

Retrofit Path & Spread



	Decorative Hammered Roof		Cast Hammered Roof																			
Finishes	TZA (shown), CO, OB		Additional Finishes	BBR (shown), TZA																		
Item Number and Finish	15443 CO 15443 OB 15443 OB12 (pack of 12) 15443 TZA	CO	15471 BBR 15471 TZA	Cast Brass (BBR) or Cast Aluminum																		
Housing																						
Lamp Base	12V S8 Wedge base socket	OB	12V S8 Wedge base socket	TZA																		
Lamp Options-Power Usage at 12V AC input	Incandescent: 18.5W(VA) 3155K (15599 CLR)	LED: 2W S8 Wedge (18036, 18037) Compares up to 18.5W Krypton 2W S8 Wedge (18202, 18203) Compares up to 20W Halogen	Incandescent: 18.5W(VA) 3155K (15599 CLR)	LED: 2W S8 Wedge (18036, 18037) Compares up to 18.5W Krypton 2W S8 Wedge (18202, 18203) Compares up to 20W Halogen																		
Wiring	35" of usable #18-2, SPT-1W leads. Cable connectors supplied.		35" of usable #18-2, SPT-1W leads. Cable connectors supplied.																			
Notes	Includes 24.4W(VA) 3156K (15598 CLR) Krypton lamp and 8" in-ground slotted stake. Features decorative light-leak pattern. LED version of fixture 15843 on page 44. Brass and Copper will naturally patina over time. U.S. Patent No. D408,573.		Includes 24.4W(VA) 3156K (15598 CLR) Krypton lamp and 8" in-ground slotted stake. Features decorative light-leak pattern. LED version of fixture 15871 on page 44. Brass will naturally patina over time.																			
Accessories	15601 Surface Mounting Flange 15607 Surface Mounting Bracket																					
Dimensions																						
Photometrics*	<table border="1"> <thead> <tr> <th>Distance from Light</th><th>1'</th><th>2'</th><th>3'</th><th>4'</th><th>5'</th><th>6'</th><th>7'</th><th>8'</th></tr> </thead> <tbody> <tr> <td>Footcandles</td><td>8.9</td><td>2.8</td><td>.6</td><td>.15</td><td>-</td><td>-</td><td>-</td><td>-</td></tr> </tbody> </table>				Distance from Light	1'	2'	3'	4'	5'	6'	7'	8'	Footcandles	8.9	2.8	.6	.15	-	-	-	-
Distance from Light	1'	2'	3'	4'	5'	6'	7'	8'														
Footcandles	8.9	2.8	.6	.15	-	-	-	-														