


TYPE ULT

Features

- Manufactured from high conductivity copper alloy
- Clearly marked with wire size and die index
- Range taking
- Suitable for use in circuits rate 35KV or less proper high voltage spacing and insulation techniques must be used
- Rated to 90° C
- UL Listed and CSA Certified for grounding and bonding

Benefits

- Provides maximum conductivity and eliminates the possibility of corrosion
- Provides easy identification and tooling recommendation
- Reduces inventory
- Application versatility
- Direct Burial in earth or concrete



Catalog Number	Copper Wire Range		Die Index	Dimensions - in. (mm)		
	Main	Tap		L	W	H
ULT-3-Z	4str-6sol	8str-8sol	BG or 5/8	.735 (18.7)	.470 (11.9)	.615 (15.6)
ULT-4-Z	4str-6sol	6str-6sol	BG or 5/8	.765 (19.4)	.460 (11.7)	.700 (17.8)
ULT-5-Z	4str-6sol	4str-4sol	BG or 5/8	.830 (21.1)	.470 (11.9)	.700 (17.8)
ULT-6-Z	2str-2sol	4str-8sol	C	.990 (25.1)	.614 (15.6)	.830 (21.1)
ULT-7-Z	2str-2sol	2str-2sol	C	1.047 (26.6)	.614 (15.6)	.826 (21.0)
ULT-8-Z	2/0str-1/0sol	2str-8sol	O	1.350 (34.3)	.812 (20.6)	.925 (23.5)
ULT-9-Z	2/0str-1/0sol	2/0str-1/0sol	O	1.350 (34.3)	.812 (20.6)	.925 (23.5)
ULT-10-Z	4/0str-3/0sol	2str-6sol	F or D3	1.628 (41.4)	1.000 (25.4)	1.075 (27.3)
ULT-11-Z	4/0str-3/0sol	2/0str-1/0sol	F or D3	1.628 (41.4)	1.000 (25.4)	1.075 (27.3)
ULT-12-Z	4/0str-3/0str	4/0str-3/0str	F or D3	1.610 (40.9)	1.000 (25.4)	1.200 (30.5)

Tooling Information

Catalog Number	Burdny				
	Y35 Die (No. of Crimps)	Y39 Die (No. of Crimps)	Y750 Die (No. of Crimps)	PAT750 Die (No. of Crimps)	Y46 Die (No. of Crimps)
ULT-3	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)
ULT-4	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)
ULT-5	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)	BG or 5/8 (1)
ULT-6	C (1)	C (1)	C (1)	C (1)	C (1)
ULT-7	C (1)	C (1)	C (1)	C (1)	C (1)
ULT-8	O (1)	O (1)	O (1)	O (1)	O (1)
ULT-9	O (1)	O (1)	O (1)	O (1)	O (1)
ULT-10	F or D3 (1)	F or D3 (1)	F or D3 (1)	F or D3 (1)	F or D3 (1)
ULT-11	F or D3 (1)	F or D3 (1)	F or D3 (1)	F or D3 (1)	F or D3 (1)
ULT-12	F or D3 (1)	F or D3 (1)	F or D3 (1)	F or D3 (1)	F or D3 (1)

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)
 Tested to UL 486A/B, UL File E6207
 Tested to UL 467, UL File E34440