

A photograph of a brick building with a covered walkway and a green geometric overlay. The building features a prominent brick wall on the left and a covered walkway with white columns on the right. The sky is blue with scattered clouds. In the foreground, there are green bushes and a concrete path. A large green geometric shape, consisting of several overlapping triangles and rectangles, is overlaid on the left side of the image, pointing towards the right.

# Outdoor

**Lumark**  
Commercial & Industrial

# Axcent LED Wall Mount Luminaire

## Lumark

The Axcent LED wall mount luminaire provides a flush-mounted, architectural design with high-performing, energy-efficient illumination. The die-cast aluminum construction along with stainless steel hardware, gasketed housing, and sealed optical compartment makes the Axcent impervious to contaminants. Ideal for building entrances, vehicle ramps, schools, tunnels, stairways, loading docks, and floodlighting applications.



AXCS1A	Small Full Cutoff	Carbon Bronze	70W HID	4000K	1,806	14	120-277V	96	080083887965	DLC Pending
AXCS1ARL	Small Refractive Lens	Carbon Bronze	70W HID	4000K	1,915	14	120-277V	96	080083887972	DLC Pending
AXCS2A	Small Full Cutoff	Carbon Bronze	100W HID	4000K	2,561	21	120-277V	96	080083887989	DLC Pending
AXCS2ARL	Small Refractive Lens	Carbon Bronze	100W HID	4000K	2,716	21	120-277V	96	080083887996	DLC Pending
AXCS3A	Small Full Cutoff	Carbon Bronze	150W HID	4000K	3,537	27	120-277V	96	080083888009	DLC Pending
AXCS3ARL	Small Refractive Lens	Carbon Bronze	150W HID	4000K	3,704	27	120-277V	96	080083888016	DLC Pending
AXCS4A	Small Full Cutoff	Carbon Bronze	250W HID	4000K	5,520	44	120-277V	96	080083888023	DLC Pending
AXCS4ARL	Small Refractive Lens	Carbon Bronze	250W HID	4000K	5,858	44	120-277V	96	080083888030	DLC Pending
AXCS5A	Small Full Cutoff	Carbon Bronze	320W HID	4000K	6,300	52	120-277V	96	080083888047	DLC Pending
AXCS5ARL	Small Refractive Lens	Carbon Bronze	320W HID	4000K	6,699	52	120-277V	96	080083888054	DLC Pending
AXCL6A	Large Full Cutoff	Carbon Bronze	320W HID	4000K	7,594	56	120-277V	45	080083811564	DLC Pending
AXCL6ARL	Large Refractive Lens	Carbon Bronze	320W HID	4000K	7,809	56	120-277V	45	080083811649	DLC Pending
AXCL8A	Large Full Cutoff	Carbon Bronze	400W HID	4000K	9,696	72	120-277V	45	080083811588	PG4TJNY3
AXCL8ARL	Large Refractive Lens	Carbon Bronze	400W HID	4000K	9,970	72	120-277V	45	080083811663	PBA84MB6
AXCL10A	Large Full Cutoff	Carbon Bronze	400W HID	4000K	13,283	102	120-277V	45	080083811601	PEEEJWAF
AXCL10ARL	Large Refractive Lens	Carbon Bronze	400W HID	4000K	13,641	102	120-277V	45	080083811687	PJAMFHC, PDOZ54B9
AXCL12A	Large Full Cutoff	Carbon Bronze	450W HID	4000K	16,823	123	120-277V	45	080083811625	PD1N4D39
AXCL12ARL	Large Refractive Lens	Carbon Bronze	450W HID	4000K	17,346	123	120-277V	45	080083811700	PYCDCLOY, PWOPA823

# Crosstour LED Wall Pack

## Lumark

The Crosstour LED wall pack series provides an architectural style with super bright, energy-efficient LEDs. The Crosstour series features low-profile, rugged die-cast aluminum construction, universal back box, stainless steel hardware along with a sealed and gasketed optical compartment, making the product impervious to contaminants. The wall luminaire is ideal for surface or inverted mount for facade/canopy illumination, post/bollard mounting and for low level pathway illumination including stairs. Typical applications include building entrances, multi-use facilities, apartment buildings, institutions, schools, stairways and loading docks.



XTOR1B	Small Full Cutoff	Carbon Bronze	70W HID	5000K	1,418	12	120-277V	240	08008377969	PRVAZAZR
XTOR2B	Small Full Cutoff	Carbon Bronze	100W HID	5000K	2,135	18	120-277V	270	080083778225	PGP4FYV3
XTOR3B	Small Full Cutoff	Carbon Bronze	150W HID	5000K	2,751	26	120-277V	270	080083778041	PWFZHYJH
XTOR4B	Medium Full Cutoff	Carbon Bronze	250W HID	5000K	4,269	38	120-277V	270	080083778003	PUJ1NXGY
XTOR6B	Large Full Cutoff	Carbon Bronze	320W HID	5000K	6,129	58	120-277V	60	080083774807	PWEKQNMV
XTOR6BRL	Large Refractive Lens	Carbon Bronze	320W HID	5000K	6,225	58	120-277V	60	080083774821	PH59ANRG
XTOR8B	Large Full Cutoff	Carbon Bronze	400W HID	5000K	8,502	81	120-277V	60	080083774814	P5557CRH
XTOR8BRL	Large Refractive Lens	Carbon Bronze	400W HID	5000K	8,635	81	120-277V	60	080083774852	P2F7Z2QT

## WP LED Glass Wall Pack

Lumark

The WP wall pack luminaire provides traditional architectural style with high performance energy efficient illumination. Rugged die-cast aluminum construction, stainless steel hardware along with a sealed and gasketed optical compartment make it virtually impenetrable to contaminants. The WP LED wall luminaire is ideal for pathway illumination, building entrances, vehicle ramps, schools, tunnels, stairways and loading docks.



WPSLED



WPMLLED



WPLLED



WPSLED-30-GL-UNV	Small Refractive Lens	Bronze	150W HID	4000K	3,382	27	120-277V	26	080083776368	PZ4PQJ7J
WPSLED-30-GL-UNV-PC	Small Refractive Lens, PC	Bronze	150W HID	4000K	3,382	27	120-277V	26	080083776528	
WPSLED-30-GL-UNV-7050	Small Refractive Lens	Bronze	150W HID	5000K	3,435	27	120-277V	26	080083776443	P2WTNDW5
WPMLLED-75-GL-UNV	Medium Refractive Lens	Bronze	320W HID	4000K	8,683	76	120-277V	72	080083776382	PAGM5GGQ
WPMLLED-75-GL-UNV-PC	Medium Refractive Lens, PC	Bronze	320W HID	4000K	8,683	76	120-277V	72	080083776542	
WPMLLED-75-GL-UNV-7050	Medium Refractive Lens	Bronze	320W HID	5000K	8,818	76	120-277V	72	080083776467	PBFHHR3H
WPLLED-100-GL-UNV	Large Refractive Lens	Bronze	400W HID	4000K	10,264	82	120-277V	48	080083776405	P6V82M4V
WPLLED-100-GL-UNV-PC	Large Refractive Lens, PC	Bronze	400W HID	4000K	10,264	82	120-277V	48	080083776566	
WPLLED-100-GL-UNV-7050	Large Refractive Lens	Bronze	400W HID	5000K	10,424	82	120-277V	48	080083776481	P2SXNNP1
WPLLED-125-GL-UNV	Large Refractive Lens	Bronze	450W HID	4000K	15,143	122	120-277V	40	080083776429	PGDAEG6T
WPLLED-125-GL-UNV-PC	Large Refractive Lens, PC	Bronze	450W HID	4000K	15,143	122	120-277V	40	080083776580	
WPLLED-125-GL-UNV-7050	Large Refractive Lens	Bronze	450W HID	5000K	15,379	122	120-277V	40	080083776504	PAKFM3BD

## WPSQLED LED Glass Wall Pack

Lumark

The WPSQLED wall-mount luminaire provides a traditional square style with high performance and energy-efficient illumination, resulting in up to 84% energy and maintenance savings over traditional MH luminaires. The rugged, die-cast aluminum construction is IP66 rated and UL/cUL wet location listed for exceptional durability and long term reliability. With lumen maintenance greater than 91% at 60,000 hours, the WPSQLED luminaire is virtually maintenance free. Replacing up to 450W MH equivalent luminaires, the WPSQLED luminaire is ideal for pathway illumination, building entrances, vehicle ramps, schools, tunnels, stairways and loading docks.



WPSQLED-65-UNV	Large Refractive Lens	Bronze	175W HID	4000K	7,108	64	120-277V	16	080083805662	PL5JKA2T2HJF
WPSQLED-65-UNV-7050	Large Refractive Lens	Bronze	175W HID	5000K	7,446	64	120-277V	16	080083805723	PLKVZN8V8BCZ
WPSQLED-65-UNV-PC	Large Refractive Lens, PC	Bronze	175W HID	4000K	7,108	64	120-277V	16	080083805907	PL5JKA2T2HJF
WPSQLED-75-UNV	Large Refractive Lens	Bronze	250W HID	4000K	7,706	75	120-277V	16	080083805686	PL88EYZWS38V
WPSQLED-75-UNV-7050	Large Refractive Lens	Bronze	250W HID	5000K	7,918	75	120-277V	16	080083805747	PL000UAIGOSF
WPSQLED-75-UNV-PC	Large Refractive Lens, PC	Bronze	250W HID	4000K	7,706	75	120-277V	16	080083805921	PL88EYZWS38V
WPSQLED-100-UNV	Large Refractive Lens	Bronze	320-450W HID	4000K	11,043	101	120-277V	16	080083805709	PL9CZYJ28FAY
WPSQLED-100-UNV-7050	Large Refractive Lens	Bronze	320-450W HID	5000K	11,322	101	120-277V	16	080083805761	PLIM3WU8Z79W
WPSQLED-100-UNV-PC	Large Refractive Lens, PC	Bronze	320-450W HID	4000K	11,043	101	120-277V	16	080083805945	PL9CZYJ28FAY

# LVL Vaportight

Lumark

The LVL LED Vaportight area luminaire provides an indoor/outdoor solution in applications where lighting fixture protection against dust and moisture is required. This fixture's traditional look and warm color temperature delivers visual comfort. The fixture is ideal for industrial and decorative residential uses including patio, garages and storage.



LVL20UG	Round, Cage Lens, Ceiling/Wall/Post Mount	Grey	3500K	1,450	18	120/277V	256	080083803637
---------	---	------	-------	-------	----	----------	-----	--------------

# CLCSLED Canopy

Lumark

The CLCSLED canopy luminaire provides a slim, low-profile, traditional design with high-performance, energy-efficient illumination. The CLCSLED luminaire seamlessly integrates into new or existing spaces including bank drive-thrus, covered side walks, hospitality entryways and retail drive-thrus.



CLCSLED-40-SM-UNV	Square Surface Mount	Bronze	150W HID	4000K	4,839	36	120-277V	144	080083776061	PCQT436Y
CLCSLED-40-SM-UNV-7050	Square Surface Mount	Bronze	150W HID	5000K	4,739	36	120-277V	144	080083776184	PSDWDZ8R
CLCSLED-40-SM-UNV-BPC	Square Surface Mount	Bronze	150W HID	4000K	4,839	36	120-277V	16	080083776269	
CLCSLED-55-SM-UNV	Square Surface Mount	Bronze	175W HID	4000K	7,230	56	120-277V	144	080083776085	PJ1SCY7M
CLCSLED-55-SM-UNV-7050	Square Surface Mount	Bronze	175W HID	5000K	6,878	56	120-277V	144	080083776207	PMYBEAJZ
CLCSLED-55-SM-UNV-BPC	Square Surface Mount, PC	Bronze	175W HID	4000K	7,230	56	120-277V	144	080083776283	PCQT436Y
CLCSLED-86-SM-UNV	Square Surface Mount	Bronze	250W HID	4000K	11,494	92	120-277V	44	080083776108	P124NMP8
CLCSLED-86-SM-UNV-7050	Square Surface Mount	Bronze	250W HID	5000K	11,279	90	120-277V	44	080083776221	PC6DN2Q7
CLCSLED-86-SM-UNV-BPC	Square Surface Mount	Bronze	250W HID	4000K	11,494	92	120-277V	44	080083776306	
CLCSLED-117-SM-UNV	Square Surface Mount	Bronze	400W HID	4000K	13,828	121	120-277V	44	080083776160	PFXC51WH
CLCSLED-117-SM-UNV-7050	Square Surface Mount	Bronze	400W HID	5000K	13,882	120	120-277V	44	080083776245	P3J2CPH2
CLCSLED-117-SM-UNV-BPC	Square Surface Mount, PC	Bronze	400W HID	4000K	13,828	121	120-277V	44	080083776320	PCQT436Y
CLCSPEND	6" Long Pendant, 3/4"							16	080083776344	

Outdoor

Commercial & Industrial

## Caretaker LED Area/Site

Lumark

The Caretaker™ LED area luminaire delivers unmatched light output and functionality in a rugged design to address low-cost, low-maintenance security lighting applications. The versatile universal mounting plate allows quick and easy installation whether it for wall mounted security lighting, residential street lighting, perimeter area lighting, parking areas, loading platforms, boat docks, access drives or pathways. The Caretaker delivers a wide, uniform distribution with excellent vertical illumination for maximum light coverage.



CTKRV1B	Area site with PC, UNV Mount Arm	Raw	150W HID	4000K	4,515	29	120-277V	54	080083865390	P3P0FHML
CTKRV2B	Area site with PC, UNV Mount Arm	Raw	175W HID	4000K	7,110	50	120-277V	54	080083865406	PREMIUM
CTKRV3B	Area site with PC, UNV Mount Arm	Raw	250W HID	4000K	9,741	71	120-277V	54	080083865413	P9E35CQB
SR-CARETAKER	Small Acrylic Refractor							240	080083699087	

## Night Falcon Floodlight

Lumark

The Night Falcon™ LED floodlight luminaire combines high-efficiency optics, superior thermal management and energy efficiency in a cost effective solution. The compact, robust design incorporates a separate driver compartment for maximum heat dissipation resulting in longer fixture and LED life. The Night Falcon luminaire uses precision engineered optics delivering superior uniformity and excellent illumination to the targeted application. Typical applications include area lighting for security, building facade lighting, accent and signage lighting in both commercial and industrial applications.



NFFLD-S-C70-KNC-UNV	Small , 6x6, Knuckle	Carbon Bronze	70W HID	4000K	2,682	20	120-277V	48	080083760282	PQEGD9D8
NFFLD-S-C70-T-UNV	Small , 6x6, Trunnion	Carbon Bronze	70W HID	4000K	2,682	20	120-277V	48	080083760299	PQEGD9D8
NFFLD-S-C15-KNC-UNV	Small , 6x6, Knuckle	Carbon Bronze	150W HID	4000K	5,797	51	120-277V	27	080083760268	P07DFEU0
NFFLD-S-C15-T-UNV	Small , 6x6, Trunnion	Carbon Bronze	150W HID	4000K	5,797	51	120-277V	36	080083760275	P07DFEU0
NFFLD-C25-S	Medium , 6x6, Slipfitter	Carbon Bronze	250W HID	4000K	10,530	85	120-277V	20	080083801244	PFT7DB3V
NFFLD-C25-T	Medium , 6x6, Trunnion	Carbon Bronze	250W HID	4000K	10,530	85	120-277V	20	080083801220	P1KJC5UE
NFFLD-C40-S	Medium , 6x6, Slipfitter	Carbon Bronze	400W HID	4000K	16,932	128	120-277V	20	080083801206	P6WY96JR
NFFLD-C40-T	Medium , 6x6, Trunnion	Carbon Bronze	400W HID	4000K	16,932	128	120-277V	24	080083801183	P1FRZ85N
NFFLD-L-C100-S	Large , 6x6, Slipfitter	Carbon Bronze	1,000W HID	4000K	33,941	252	120-277V	6	080083800889	PXL241RW
NFFLD-L-C100-T	Large , 6x6, Trunnion	Carbon Bronze	1,000W HID	4000K	33,941	252	120-277V	6	080083800902	PWOBVSIR

# PRV Prevail LED Area/Site

## Lumark

The Prevail™ LED area/site luminaire delivers a new level of performance, versatility and value in a low-profile, patent-pending, architectural design that delivers significant installation and energy savings. A versatile mount arm makes retrofit installation simple, resulting in reduced installation time and additional labor savings. Ideal for general area lighting applications such as parking lots, walkways, roadways and building areas.



Outdoor

Commercial & Industrial

PRVS-A15-UNV-T3	T3 Distr. STD Arm Mount	Bronze	150W HID	4000K	6,192	57	120-277V	16	080083746217	P822WFYF
PRVS-A15-UNV-T4	T4 Distr., STD Arm Mount	Bronze	150W HID	4000K	6,173	57	120-277V	16	080083753499	PX98J82E
PRVS-A15-UNV-T3-MSP/DIM-L30	T3 Distr., STD Arm Mount, Integrated Dimming Sensor	Bronze	150W HID	4000K	6,192	57	120-277V	16	080083745715	P822WFYF
PRVS-A25-UNV-T3	T3 Distr., STD Arm Mount	Bronze	250W HID	4000K	10,292	87	120-277V	16	080083746224	PPJY8QDC
PRVS-A25-UNV-T4	T4 Distr., STD Arm Mount	Bronze	250W HID	4000K	10,261	87	120-277V	16	080083753482	PWDY6EFH
PRVS-A25-UNV-T3-MSP/DIM-L30	T3 Distr., STD Arm Mount, Integrated Dimming Sensor	Bronze	250W HID	4000K	10,292	87	120-277V	16	080083745722	PPJY8QDC
PRVS-A40-UNV-T3	T3 Distr., STD Arm Mount	Bronze	400W HID	4000K	15,203	143	120-277V	16	080083746231	PKBPW82Y
PRVS-A40-UNV-T4	T4 Distr., STD Arm Mount	Bronze	400W HID	4000K	15,157	143	120-277V	16	080083753475	PGFRK6CU
PRVS-A40-UNV-T3-MSP/DIM-L30	T3 Distr., STD Arm Mount, Integrated Dimming Sensor	Bronze	400W HID	4000K	15,203	143	120-277V	16	080083745739	PKBPW82Y
PRVS-A60-UNV-T3	T3 Distr., STD Arm Mount	Bronze	450W HID	4000K	18,992	163	120-277V	16	080083773695	<b>PDRYNOXX</b>
PRVS-A60-UNV-T4	T4 Distr., STD Arm Mount	Bronze	450W HID	4000K	18,935	163	120-277V	16	080083773701	PA43W7HY
PRVS-A60-UNV-T3-MSP/DIM-L30	T3 Distr., STD Arm Mount, Integrated Dimming Sensor	Bronze	450W HID	4000K	18,992	163	120-277V	16	080083773732	<b>PDRYNOXX</b>
PRVS-A60-UNV-T4-MSP/DIM-L30	T4 Distr., STD Arm Mount, Integrated Dimming Sensor	Bronze	450W HID	4000K	18,935	163	120-277V	16	080083788163	PA43W7HY

