


AC/MC CABLE FITTINGS



WHEN YOU'RE
RUNNING CABLE,
RUN WITH THE BEST.

BRIDGEPORT
CABLE FITTINGS.

 **BRIDGEPORT**
www.bptfittings.com



SELECTION AND INNOVATION.


GET ALL YOUR AC/MC
CABLE JOBS DONE FAST,
AND DONE RIGHT
WITH BRIDGEPORT.

Quality, innovation, selection and availability – you get it all with the industry's leading AC/MC cable fittings line from Bridgeport. So all the choices you need in steel, malleable and zinc share the most important product attribute: *a Bridgeport Circle B on the fitting.* It's the mark that says you take pride in your work.

From duplex snap-ins and single and double screw connectors to transition couplings and universal straps with stronger straps – Bridgeport's got you covered. We've engineered in performance differences that can help you every day – better fit, faster install and assured quality out of the box. Plus, innovations like deep-slot tri-head screws, tapped locknuts that don't "jump" threads and snap-ins that snap out easy, too.

Make the smart selection and choose Bridgeport cable fittings every time. For installations that last a lifetime. Call Bridgeport at 203-377-5944 or visit us online at www.bptfittings.com and be sure all your AC and MC connections are A-OK.


Because the sure way to spell AC/MC success is with a B. Bridgeport.



FEATURED PRODUCT:

**WHIPPER-SNAP® Snap-in "U"
Shaped Strap Duplex Connector
(SG3838ASP)**

Connect two 14/2 to 10/3 AC/MC cables or 3/8" flexible metal conduit to a box or enclosure. Simply push the connector into the box for a quick, secure connection every time.



WHIPPER-SNAP® FITTINGS

YOUR BEST SOURCE FOR PATENTED SNAP-IN FITTINGS

Save time and money with every installation.

WHIPPER-SNAP fittings snap right into the box – with the satisfying click of performance.

Convenience.

Pre-assemble cable, or easily install after connector is in the box. Either way, assembly is a snap. You can remove WHIPPER-SNAP connectors almost as easy as you pop them in. Simply depress the tab with a flat blade screwdriver.


Designed to work the way you work.

On the job, you'll appreciate the attention to detail and the many convenient features that make the whole WHIPPER-SNAP line so easy to use.

In AND out in a snap.

You thought they installed fast?

Just press, tilt and remove. Our snap-in fittings remove as fast as they snap in – ready to reuse.



Large Feeder Cable Fittings

Bridgeport's AC/MC Connectors are the industry's finest choice for connecting large branch circuit or feeder MC Cable to boxes, enclosures, load-centers, panelboards, transformers, switchgear, and other electrical equipment. Use Bridgeport's fittings to obtain a robust mechanical connection in commercial and industrial facilities such as paper mills, chemical plants, utility plants, educational facilities, office buildings as well as multi-family, residential complexes.



403-DC2

AC/MC Selection Chart

Catalog Number	UPC Number	Trade Size	K.O. Size	Cable
----------------	------------	------------	-----------	-------

DIE CAST SQUEEZE CONNECTORS

403-DC2	15403	3/8"	1/2"	12/3 thru 10/3 (.58"-.61") AC/MC
---------	-------	------	------	----------------------------------

DIE CAST STRAP TYPE CONNECTORS

560-DC2	15560	3/8"	1/2"	14/4 to 10/4 (.44"-.61") AC/MC/MCI-A
561-DC2	15561	3/4"	3/4"	12/4 thru 8/4 (.61"-.87") AC/MC
560-DCI2	16560	3/8"	1/2"	14/4 to 10/4 (.43"-.61") AC/MC/MCI-A
561-DCI2	16561	3/4"	3/4"	AC/MC: 12/4 thru 8/4 (.61"-.87") AC/MC
560-MCIA2	72560	3/8"	1/2"	14/2 to 10/4 (.38"-.61") MCI-A
560ASP	08560	3/8"	1/2"	14/2 to 10/3 (.43"-.61") AC/MC/MCI-A (Whipper-Snap®)
560MCIA	71560	3/8"	1/2"	14/2 to 10/4 (.42"-.61") AC/MC/MCI-A (Whipper-Snap)
560SP	70560	3/8"	1/2"	14/2 to 10/3 (.43"-.61") AC/MC (Whipper-Snap)
BL-17	15567	1/2"	1/2"	8/3 AC90, 8/3 or 6/3 MCI-A
BL-17I	16567	1/2"	1/2"	8/3 AC90, 8/3 or 6/3 MCI-A
BL-18	15568	3/4"	3/4"	6/3 AC90
BL-18I	16568	3/4"	3/4"	6/3 AC90
BL-19	15569	1"	1"	3/3 AC90
BL-19I	16569	1"	1"	3/3 AC90



560-DC2

561-DCI2



560ASP



560SP



BL-17



501-DC2

545-DC2

563-DC2



565-DC2

566-DC2

840SP



845ASP

845SP

8400SP

DIE CAST 1 OR 2 SCREW CONNECTORS

501-DC2	15501	3/8"	1/2"	14/2-10/3 Steel MC/MCI-A .43"-.61" Steel or AL AC
545-DC2	15545	3/8"	1/2"	14/2 thru 10/3 (.44"-.61") AC/MC
563-DC2	15563	3/8"	1/4"	14/2-12/2 AC/MC/NM
565-DC2	15565	3/8"	1/2"	14/2 to 10/3 (.38"-.53") MC/MCI-A
566-DC2	15566	3/8"	1/2"	14/4 to 10/3 (.44"-.53") ALMC/MCI-A
845ASP	08501	3/8"	1/2"	12/2 to 10/4 (.43"-.61") AC/MC/MCI-A
845SP	70501	3/8"	1/2"	12/2 to 10/4 (.43"-.61") AC/MC/MCI-A
840SP	70566	3/8"	1/2"	14/2 to 10/3 (.44"-.61") AC/MC/MCI-A
8400SP	70565	3/8"	1/2"	14/4 to 10/3 (.44"-.61") AC/MC/MCI-A (Whipper-Snap)
8400ASP	71565	3/8"	1/2"	14/2 to 10/3 (.38"-.53") AC/MC/MCI-A (Whipper-Snap)



403-I

Catalog Number	UPC Number	Trade Size	K.O. Size	Cable
----------------	------------	------------	-----------	-------

MALLEABLE IRON SINGLE SCREW CONNECTORS

403-I	10403	3/8"	1/2"	14/4 to 6/3 AC/MC/MCI-A
-------	-------	------	------	-------------------------


 SG38ASP
 SG38MCIA

SG38SP

DIE CAST LOW PROFILE "U" SHAPED STRAP CONNECTORS

SG38ASP	08570	3/8"	1/2"	14/4 to 10/3 (.43"-.61") AC/MC/MCI-A (Whipper-Snap)
---------	-------	------	------	---

SG38MCIA	71570	3/8"	1/2"	14/2 to 10/3 (.38"-.56") AC/MC/MCI-A (Whipper-Snap)
----------	-------	------	------	---

SG38SP	70570	3/8"	1/2"	14/4 to 10/3 (.43"-.61") AC/MC/MCI-A (Whipper-Snap)
--------	-------	------	------	---



570-DC2

570-DCI2

570-DC2	15570	3/8"	1/2"	14/2 to 10/3 (.38"-.61") AC/MC/MCI-A
---------	-------	------	------	--------------------------------------

570-DCI2	16570	3/8"	1/2"	14/4 to 10/3 (.38"-.61") AC/MC/MCI-A
----------	-------	------	------	--------------------------------------



570-RI

 570-GI
 570-G/RI

DIE CAST COLOR-CODED LOW PROFILE CONNECTORS

570-GI	75706	3/8"	1/2"	14/2 to 10/3 (.38"-.61") HCF/AC (Green color)
--------	-------	------	------	---


570-RI	75708	3/8"	1/2"	18/2 to 12/4 (.38"-.61") Fire Alarm MC (Red color)
--------	-------	------	------	--

DIE CAST 2 SCREW CONNECTORS


653-DC2	15653	1/2"	1/2"	8/2-6/4 (.675"-.90") AC
---------	-------	------	------	-------------------------

655-DC2	15655	3/4"	3/4"	6/3-4/3 (.85"-1.1") AC/MC
---------	-------	------	------	---------------------------

657-DC2	15657	1"	1"	4/3 to 1/3 (1.03"-1.31") AC/MC
---------	-------	----	----	--------------------------------


 653-DC2
 657-DC2

657-DC2



Catalog Number	UPC Number	Trade Size	K.O. Size	Cable
----------------	------------	------------	-----------	-------

DIE CAST LARGE SIZE 2 SCREW, STRAP TYPE CONNECTORS

682-DC2	15682	3/4"	1"	3 #12 to 3 #6 (.525"-.875") AC/MC
683-DC2	15683	1"	1"	3 #4 to 4 #3 (.875"-1.04") MC
683-DCI2	16683	1"	1"	3 #6 to 3 #3 (.75"-1.04") MC
683-DCX2	15683	1"	1"	3 #4 to 4 #3 (.88"-1.04") AC/MC
684-DC2	15684	1 1/4"	1 1/4"	3 #1 to 4 #2 (1.1"-1.25") MC
684-DCX2	15684	1 1/4"	1 1/4"	3 #1 to 4 #2 (1.1"-1.25") AC/MC
685-DC2	15685	1 1/2"	1 1/2"	3 #2/0 to 4 #1/0 (1.25"-1.5") MC
685-DCX2	15685	1 1/2"	1 1/2"	3 #2/0 to 4 #1/0 (1.25"-1.5") AC/MC
686-DC2	15686	2"	2"	3 #350 to 4 #250 (1.75"-2.0") MC
686-DCX2	25686	2"	2"	3 #4/0 to 4 #250 (1.5"-1.85") MC
687-DC2	15687	2 1/2"	2 1/2"	3 #500 to 4 #400 (2.0"-2.5") MC
687-DCX2	15687	2 1/2"	2 1/2"	3 #500 to 4 #400 (2.0"-2.5") AC/MC
688-DC2	15688	3"	3"	3 #600 to 4 #700 (2.375"-3.0") MC
688-DCX2	15688	3"	3"	3 #600 to 4 #700 (2.38"-3.0") AC/MC
689-DC2	15689	3 1/2"	3 1/2"	4 #700 to 4 #750 (2.75"-3.50") MC
689-DCX2	15689	3 1/2"	3 1/2"	4 #700 to 4 #750 (2.75"-3.5") AC/MC

MALLEABLE IRON (REGULAR OPENING) 4 SCREW, STRAP TYPE CONNECTORS



683-XM	00683	1"	1"	3 # 4 to 4 #3 (.81"-1.05") AC/MC
684-XM	00684	1 1/4"	1 1/4"	3 #1 to 4 #2 (1.05"-1.27") AC/MC
685-XM	00685	1 1/2"	1 1/2"	3 #2/0 to 4 #1/0 (1.27"-1.4") AC/MC
686-XM	00686	2"	2"	3-4/0 to 3 #250 (1.4"-1.94") AC/MC
687-XM	00687	2 1/2"	2 1/2"	3 #500 to 4 #400 (1.94"-2.40") AC/MC
688-XM	00688	3"	3"	3 #600 to 4 #700 (2.4"-2.9") AC/MC
689-XM	00689	3 1/2"	3 1/2"	4 #700 to 4 #750 (2.6"-3.2") AC/MC

DIE CAST 90° CONNECTORS




801-DC2	15801	3/8"	1/2"	12/2 to 10/3 (.45"-.625") MC
801-DCI2	16801	3/8"	1/2"	12/2 to 10/3 (.45"-.625") MC
802-MCIA2	75802	3/8"	1/2"	(.42"-.55") MC/MCI-A
802MCI-A	71802	3/8"	1/2"	(.42"-.55") MC/MCI-A (Whipper-Snap)
802-DC2	15802	3/8"	1/2"	12/2 to 10/3 (.48"-.58") AC/MC
802-DCI2	16802	3/8"	1/2"	12/2 to 10/3 (.48"-.58") AC/MC
802ASP	08802	3/8"	1/2"	12/2 to 10/3 (.48"-.58") AC/MC (Whipper-Snap)
802SP	70802	3/8"	1/2"	12/2 to 10/3 (.48"-.58") AC/MC (Whipper-Snap)


Catalog Number	UPC Number	Trade Size	K.O. Size	Cable
----------------	------------	------------	-----------	-------

DIE CAST 90° CONNECTORS continued

807-DC2	15807	1"	1"	1.187" to 1.312" MC
808-DC2	15808	1 1/4"	1 1/4"	1.500" to 1.625" MC
807-DCI2	16807	1"	1"	1.187" to 1.312" MC
808-DCI2	16808	1 1/4"	1 1/4"	1.500" to 1.625" MC
804-DC2	15804	1/2"	1/2"	8/4 to 6/3 (.75"-.875") MC
804-DCI2	16804	1/2"	1/2"	8/4 to 6/3 (.75"-.875") MC
806-DC2	15806	3/4"	3/4"	4/2 to 4/3 (.875"-1.0") MC
806-DCI2	16806	3/4"	3/4"	4/2 to 4/3 (.875"-1.0") MC
830-DC2	15830	3/8"	1/2"	14/2 to 10/3 (.44"-.61") AC
850SP	70801	3/8"	1/2"	12/2 to 10/3 (.55"-.61") MC (Whipper-Snap)
851ASP	08851	1/2"	1/2"	1/2" FMC (Whipper-Snap)
851-DC2	15851	1/2"	1/2"	1/2" FMC
851-DCI2	16851	1/2"	1/2"	1/2" FMC
851SP	70851	1/2"	1/2"	1/2" FMC (Whipper-Snap)
84690SP	70830	3/8"		14/2 to 10/3 (.42"-.61") AC/MC/MCI-A


CABLE BRACKETS

895-MC	02895		14/2 to 12/3 (.475"-.59") AC/MC
NMCB-1	40747		14/2, 12/2 NM
NMCB-3	40767		14/2, 10/3 NM



STEEL 1-HOLE STRAPS

890-MC	02890		14/2 to 12/2 (.475"-.525") AC/MC
891-MC	02891		14/3 to 12/3 (.54"-.59") AC/MC
900F	02970		12/4 to 10/3 (.56"-.61") AC/MC
US-4461	02892	3/8"	14/2 to 10/3 MCI-A (.425"-.61") AC/MC

COMBINATION EMT - AC/MC COUPLING

4157-DC	94157		14/2 thru 10/3 to 3/4" EMT (.42"-.61") AC/MC
---------	-------	--	--





Catalog Number	UPC Number	Trade Size	K.O. Size	Cable
----------------	------------	------------	-----------	-------

STEEL E-Z LOCK SINGLE & DUPLEX CONNECTORS

AMC-50	20570	3/8"	1/2"	14/4 to 10/4 (.40"-.62") AC/MC/MCI-A
AMC-5075	20577	1/2"	1/2"	8/3 to 6/2 (.62"-.92") AC/MC/MCI-A
AMC-52	20580	3/8"	1/2"	14/4 to 10/4 (.43"-.62") AC/MC/MCI-A
AMC-75	20571	3/4"	3/4"	10/3 to 8/4 (.566"-.81") AC/MC/HCF

"U" SHAPED STRAP CONNECTORS


571-DC2	15571	1/2"	1/2"	8/3 to 6/3 (.70"-.855") AC/MC/MCI-A
571-DCI2	16571	1/2"	1/2"	8/3 to 6/2 (.63"-.78") AC/MC/MCI-A
572-DC2	15572	3/4"	3/4"	4/3 to 3/4 (.948"-1.035") AC/MC
573-DC2	15573	1"	1"	2/3 to 2/0-3 (1.18"-1.35") AC/MC
571-S	00571	1/2"	1/2"	8/3 to 6/3 (.701"-.855") AC/MC/MCI-A
571-SI	10571	1/2"	1/2"	8/3 to 6/2 (.63"-.78") AC/MC/MCI-A
572-S	00572	3/4"	3/4"	4/3 to 3/4 (.945"-1.12") AC/MC
573-S	00573	1"	1"	2/3 to 2/0-3 (1.18"-1.35") AC/MC

DIE CAST SNAP-IN CONNECTORS

38ASP (Whipper-Snap)	08590	3/8"	1/2"	14/4 to 10/4 (.43"-.61") AC/MC/MCI-A
380SP (Whipper-Snap)	70590	3/8"	1/2"	14/4 to 10/4 (.43"-.61") AC/MC/MCI-A
590-DC2	15590	3/8"	1/2"	14/2 to 10/3 (.43"-.61") AC/MC
590-DCI2	16590	3/8"	1/2"	14/2 to 10/3 (.43"-.61") AC/MC

DIE CAST CONNECTORS FOR PVC & TECK JACKETED MC

595-DC2	15595	3/8"	1/2"	12/3 thru 10/3 PVC Jacketed MC or 14/2, 14/3 or 12/2 TECK Cable with Armor and Jacket (.5"-.61")
595-DCI2	16595	3/8"	1/2"	12/3 thru 10/3 PVC Jacketed MC or 14/2, 14/3 or 12/2 TECK Cable with Armor and Jacket (.5"-.61")
596-DC2	15596	1/2"	1/2"	10/3 thru 8/3 PVC Jacketed MC or 14/2 thru 10/3 TECK Cable with Armor and Jacket (.685"-.80")
596-DCI2	16596	1/2"	1/2"	10/3 thru 8/3 PVC Jacketed MC or 14/2 thru 10/3 TECK Cable with Armor and Jacket (.685"-.80")





USS-6171



830-DC2



601-DC2



3838SP



846SP



3838ASP



SG3838ASP

Catalog Number	UPC Number	Trade Size	K.O. Size	Cable
----------------	------------	------------	-----------	-------

STEEL STRAPS FOR PVC AND TECK JACKETED MC

USS-6171	02893	3/8"	1/2"	(.61"-.71") AC/MC/PVC-MC
----------	-------	------	------	--------------------------

DIE CAST DUPLEX CONNECTORS

601-DC2	15601	3/8"	1/2"	14/2 to 10/4 (.375"-.625") AC/MC/MCI-A
691-DC2	15691	3/8"	1/2"	14/2 to 10/3 (.42"-.61") AC/MC/MCI-A
830-DC2	15830	3/8"	1/2"	14/2 to 10/3 (.44"-.61") AC/MC
846SP	70601	3/8"	1/2"	14/4 to 10/4 (.375"-.625") AC/MC/MCI-A (Whipper-Snap)
3838ASP	08690	3/8"	1/2"	14/4 to 10/4 (.38"-.59") AC/MC/MCI-A (Whipper-Snap)
3838SP	70690	3/8"	1/2"	14/4 to 10/4 (.38"-.59") AC/MC/MCI-A (Whipper-Snap)
SG3838ASP	08691	3/8"	1/2"	14/4 to 10/4 (.42"-.61") AC/MC/MCI-A

Suggested Fittings for Non-PVC Jacketed MC Cable
3 CONDUCTORS WITH GROUND

Size (AWG or kcmil)	Bridgeport Connector
6-6-6-6	653-DC2
4-4-4-6	683-DC2
2-2-2-4	683-DC2
1-1-1-4	684-DC2
1/0-1/0-1/0-4	684-DC2
2/0-2/0-2/0-4	685-DC2
3/0-3/0-3/0-4	685-DC2
4/0-4/0-4/0-2	686-DCX2
250-250-250-2	686-DCX2
300-300-300-1	686-DC2
350-350-350-1	686-DC2
400-400-400-1	687-DC2
500-500-500-1	687-DC2
500-500-500-2/0	687-DC2
500-500-500-250	688-DC2
600-600-600-1/0	687-DC2
750-750-750-1/0	688-DC2
750-750-750-3/0	688-DC2

4 CONDUCTORS WITH GROUND

Size (AWG or kcmil)	Bridgeport Connector
6-6-6-6-6	653-DC2
4-4-4-4-6	683-DC2
2-2-2-2-4	657-DC2
1-1-1-1-4	684-DC2
1/0-1/0-1/0-1/0-4	685-DC2
2/0-2/0-2/0-2/0-4	685-DC2
3/0-3/0-3/0-3/0-4	686-DCX2
4/0-4/0-4/0-4/0-2	686-DCX2
250-250-250-250-1	686-DC2
300-300-300-300-1	687-DC2
350-350-350-350-1/0	687-DC2
400-400-400-400-3/0	687-DC2
500-500-500-500-3/0	687-DC2
500-500-500-500-250	687-DC2
600-600-600-600-3/0	688-DC2
600-600-600-600-400	688-DC2
750-750-750-750-3/0	688-DC2
750-750-750-750-500	689-DC2
900-900-900-900-250	689-DC2

Bridgeport MCI-A Cable Fittings

Cable Fitting	Enclosure Opening KO Size	Cable Outer Diameter (O.D.) Range	Cable Types Listed To:	Healthcare Facility Cable	Flexible Metal Conduit	Recommended Cable Types
			Note: Includes Steel and Aluminum		Note: Includes Steel and Aluminum (RWFMC)	Note: Verify with cable O.D. Includes Steel and Aluminum
38ASP	1/2"	.43-.61	AC/MC/MCIA	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
380SP	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
3838ASP	1/2"	.38-.59	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/2
3838SP	1/2"	.38-.59	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/2
403-DC2	1/2"	.56-.61	AC/MC	HCF	3/8" FMC	12/3 to 10/3
407-DC2	1/2"	.86-.92	AC	HCF		
407-DCI2	1/2"	.86-.92	AC	HCF		
501-DC2	1/2"	.43-.61	MC ONLY			14/2 - 10/3
545-DC2	1/2"	.44-.61	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 - 10/3
560ASP	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
560-DC2	1/2"	.44-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	12/2 to 10/4
560-DCI2	1/2"	.44-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	12/2 to 10/4
560MCIA	1/2"	.38-.55	MC/MCI-A	HCFMCI-A		14/2 - 10/3
560-MCIA2	1/2"	.38-.61	MC/MCI-A	HCFMCI-A		14/2 to 10/3
560SP	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
561-DC2	3/4"	.61-.87	AC/MC	HCF		10/4 to 8/3
561-DCI2	3/4"	.61-.87	AC/MC	HCF		10/4 to 8/3
563-DC2	1/4"		AC/MC	HCF		14/2 to 12/2
565-DC2	1/2"	.38-.53	MC/MCI-A	HCFMCI-A		14/2 to 10/3
566-DC2	1/2"	.44-.53	AC/MC/MCI-A	HCF/HCFMCI-A		12/2 to 10/3
570-DC2	1/2"	.38-.61	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 to 10/3
570-DCI2	1/2"	.38-.61	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 to 10/3
570-DCR2	1/2"	.38-.61	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 to 10/3
570-GI	1/2"	.38-.61	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 to 10/3
570-RI	1/2"	.38-.61	AC/MC/MCI-A	HCF/HCFMCI-A		18/2 - 12/4
571-DC2	1/2"	.70-.855	AC/MC/MCI-A	HCF/HCFMCI-A	1/2" FMC	8/3 - 6/3
571-DCI2	1/2"	.70-.855	AC/MC/MCI-A	HCF/HCFMCI-A	1/2" FMC	8/3 - 6/3
571-S	1/2"	.701-.855	MC/MCI-A	HCFMCI-A	1/2" FMC	8/3 - 6/3
571-SI	1/2"	.701-.855	MC/MCI-A	HCFMCI-A	1/2" FMC	8/3 - 6/3
572-DC2	3/4"	.945-1.035	MC		3/4" FMC	4/3 - 3/4
572-DCI2	3/4"	.945-1.035	MC		3/4" FMC	4/3 - 3/4
572-S	3/4"	0.945	MC		3/4" FMC	4/3
572-SI	3/4"	0.945	MC		3/4" FMC	4/3
573-DC2	1"	1.18-1.35	MC		1" FMC	2/3 - 3 2/0
573-DCI2	1"	1.18-1.35	MC		1" FMC	2/3 - 3 2/0
573-S	1"	1.18-1.35	MC		1" FMC	2/3 - 3 2/0
573-SI	1"	1.18-1.35	MC		1" FMC	2/3 - 3 2/0
590-DC2	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
590-DCI2	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
595-DC2	1/2"	.50-.61	JMC/ TECK90			12/2 - 10/3
595-DC2C	1/2"	.50-.61	JMC/ TECK90			12/2 - 10/3
595-DCI2	1/2"	.50-.61	JMC/ TECK90			12/2 - 10/
596-DC2	1/2"	.61-.69	JMC/ TECK90			10/4 to 8/3
596-DC2C	1/2"	.61-.69	JMC/ TECK90			10/4 to 8/3
596-DCI2	1/2"	.61-.69	JMC/ TECK90			10/4 to 8/3
601-DC2	1/2"	.375-.625	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
653-DC2	1/2"	.675-.90	AC	HCF	1/2" FMC	8/2 - 6/4
655-DC2	3/4"	.85-1.10	AC/MC	HCF	3/4" FMC	6/3 - 4/3
657-DC2	1"	1.03-1.31	AC/MC	HCF	1" FMC	4/3 - 1/3
682-DC2	3/4"	.575-.875	AC/MC	HCF		10/3 to 6/4
683-DC2	1"	.875-1.04	MC			6/4 to 4/3
684-DC2	1-1/4"	1.1-1.25	MC			4/4 to 3/4
685-DC2	1-1/2"	1.25-1.5	MC			2/4 to 3-2/0
686-DC2	2"	1.75-2.00	MC			4-4/0 to 4-250 MCM
687-DC2	2-1/2"	2-2.5	MC			4-300 MCM to 4-500 MCM
688-DC2	3"	2.375-3	MC			4-500 MCM to 4-750 MCM
689-DC2	3-1/2"	2.75-3.50	MC			4-600 MCM to 4-750 MCM
683-DCI2	1"	.750-1.04	MC			6/4 to 4/3
684-DCI2	1-1/4"	1.1-1.25	MC			4/4 to 3/4
685-DCI2	1-1/2"	1.25-1.5	MC			2/4 to 3-2/0
686-DCI2	2"	1.75-2.00	MC			4-4/0 to 4-250 MCM
687-DCI2	2-1/2"	2-2.5	MC			4-300 MCM to 4-500 MCM

Bridgeport MCI-A Cable Fittings

Cable Fitting	Enclosure Opening KO Size	Cable Outer Diameter (O.D.) Range	Cable Types Listed To: Note: Includes Steel and Aluminum	Healthcare Facility Cable	Flexible Metal Conduit Note: Includes Steel and Aluminum (RWFMC)	Recommended Cable Types Note: Verify with cable O.D. Includes Steel and Aluminum
688-DCI2	3"	2.375-3	MC			4-500 MCM to 4-750 MCM
689-DCI2	3-1/2"	2.75-3.50	MC			4-600 MCM to 4-750 MCM
683-DCX2	1"	.875-1.04	MC			6/4 to 4/3
684-DCX2	1-1/4"	1.1-1.25	MC			4/4 to 3/4
685-DCX2	1-1/2"	1.25-1.5	MC			2/4 to 3-2/0
686-DCX2	2"	1.5-1.85	MC			3-4/0 to 4-250 MCM
687-DCX2	2-1/2"	2-2.5	MC			4-300 MCM to 4-500 MCM
688-DCX2	3"	2.375-3	MC			4-500 MCM to 4-750 MCM
689-DCX2	3-1/2"	2.75-3.50	MC			4-600 MCM to 4-750 MCM
683-XM	1"	0.81-1.05	AC/MC	HCF		6/4 to 4/3
684-XM	1-1/4"	1.05-1.27	AC/MC	HCF		4/4 to 3/4
685-XM	1-1/2"	1.27-1.4	AC/MC	HCF		4-2/0 to 3-350 MCM
686-XM	2"	1.4-1.94	AC/MC	HCF		3-4/0 to 4-250 MCM
687-XM	2-1/2"	1.94-2.4	MC			4-300 MCM to 4-500 MCM
688-XM	3"	2.4-2.9	MC			4-500 MCM to 4-750 MCM
689-XM	3-1/2"	2.6-3.2	MC			4-600 MCM to 4-750 MCM
691-DC2	1/2"	.42-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
801-DC2	1/2"	.45-.625	MC/MCI-A	HCFMCI-A	3/8" FMC	14/4 - 10/4
802ASP	1/2"	.48-.58	AC/MC	HCF	3/8" FMC	12/2 to 10/3
802-DC2	1/2"	.48-.58	AC/MC	HCF	3/8" FMC	12/2 to 10/3
802-DCI2	1/2"	.48-.58	AC/MC	HCF	3/8" FMC	12/2 to 10/3
802SP	1/2"	.48-.58	AC/MC	HCF	3/8" FMC	12/2 to 10/3
802MCIA	1/2"	.42-.55	MC/MCI-A	HCFMCI-A		14/4 to 10/3
802-MCIA2	1/2"	.42-.55	MC/MCI-A	HCFMCI-A		14/4 to 10/3
804-DC2	1/2"	.75-.875	MC		1/2" FMC	
804-DCI2	1/2"	.75-.875	MC		1/2" FMC	
806-DC2	3/4"	.875-1.00	MC		3/4" FMC	
806-DCI2	3/4"	.875-1.00	MC		3/4" FMC	
807-DC2	1"	1.187-1.312	MC		1" FMC	
807-DCI2	1"	1.187-1.312	MC		1" FMC	
808-DC2	1-1/4"	1.50-1.625	MC		1-1/4" FMC	
808-DCI2	1-1/4"	1.50-1.625	MC		1-1/4" FMC	
830-DC2	1/2"	.44-.61	AC	HCF	3/8" FMC	12/2 - 10/3
8400ASP	1/2"	.38-.525	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 - 12/3
8400SP	1/2"	.38-.61	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 - 10/3
840SP	1/2"	.44-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/4 - 10/3
845ASP	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 - 10/3
845SP	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A		14/2 - 10/3
84690SP	1/2"	.42-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/4 - 10/3
846SP	1/2"	.38-.625	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/4
850SP	1/2"	.55-.61	AC/MC	HCF	3/8" FMC	12/2 - 10/3
851ASP	1/2"				1/2" FMC	
851-DC2	1/2"				1/2" FMC	
851-DCI2	1/2"				1/2" FMC	
851SP	1/2"				1/2" FMC	
895-DC2	1/2"	.50-.61	JMC/ TECK90			12/2 - 10/3
895-DCI2	1/2"	.50-.61	JMC/ TECK90			12/2 - 10/3
AMC-50	1/2"	.40-.62	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 to 10/3
AMC-5075	1/2"	.62-.92	AC/MC/MCI-A	HCF/HCFMCI-A	1/2" FMC	10/4 to 6/4
AMC-52	1/2"	.43-.62	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 to 10/3
AMC-75	3/4"	.56-.81	AC/MC	HCF	1/2" FMC	10/3 - 6/3
BL-17	1/2"	.701-803	8/3 AC90	HCF	1/2" FMC	8/3 - 6/3
BL-17I	1/2"	.701-803	8/3 AC90	HCF	1/2" FMC	8/3 - 6/3
BL-18	3/4"		6/3 AC90 ONLY		3/4" FMC	6/3
BL-18I	3/4"		6/3 AC90 ONLY		3/4" FMC	6/3
BL-19	1"		3/3 AC90		1" FMC	3/3
BL-19I	1"		3/3 AC90		1" FMC	3/3
SG3838ASP	1/2"	.42-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/2 - 10/3
SG38ASP	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/4 - 10/3
SG38SP	1/2"	.43-.61	AC/MC/MCI-A	HCF/HCFMCI-A	3/8" FMC	14/4 - 10/3
SG38MCIA	1/2"	.38-.56	MC/MCI-A	HCFMCI-A		14/2 - 10/3



BUY AMERICAN. BUY BRIDGEPORT.


Stimulus from Bridgeport.

When you think American, think Bridgeport. We're investing in our U.S.-based manufacturing operation in Stratford, Connecticut. We're investing in equipment, improving process automation and developing new products – all in the U.S. And still today, nearly three-quarters of our product volume is manufactured in the U.S. Find the American-made products for your projects at: www.bptfittings.com/american



**OUR DNA
IS IN EVERY BOX®**

Distributed by:



Bridgeport Fittings, Inc.
705 Lordship Blvd.
Stratford, CT 06615-7313

Voice: 203.377.5944
Fax: 203.381.3488
E-mail: sales@bptfittings.com

www.bptfittings.com



Printed in the U.S.A.

© 2012 Bridgeport Fittings, Inc. All rights reserved.

WHIPPER-SNAP and 38 Special are trademarks of Bridgeport Fittings, Inc.



02/12 7500 BP070