

Features & Benefits

Type A Application:

- Works on existing compatible Instant Start, Programmed Start, Dimming electronic ballast

Type B Application:

- Internal Driver (Direct 120-277VAC input)
- Long life | High CRI
- Instant on, no delay
- Convenient and quick installation
- Utilizes existing instant start or rapid start sockets
- Compatible with controls and sensors
- Works in cold temperature applications
- Glass tube for superior optical performance
- 5 Year Warranty



* EMERGENCY BALLAST RESTRICTIONS




UniFlex™

Commercial Grade LED T8 Lamp

Specification Data (with Normal Ballast Factor)

Order Code	Length	Input Voltage	Power Direct AC	Power w/ Ballast	CCT	Lumen	CRI	Beam Angle	Lamp Efficacy Direct AC	System Efficacy w/ Ballast	Life	DLC
L24T8/830/9G-AB	24	120-277V	9	12	3000K	1350	83	325	150	112	50000	Yes
L24T8/835/9G-AB	24	120-277V	9	12	3500K	1350	83	325	150	112	50000	Yes
L24T8/840/9G-AB	24	120-277V	9	12	4000K	1350	83	325	150	112	50000	Yes
L24T8/850/9G-AB	24	120-277V	9	12	5000K	1350	83	325	150	112	50000	Yes

Wiring diagram



* Please refer to this ["Ballast Compatibility List"](#) for compatible models.

Specification data is based on tests performed in a controlled environment and represents relative performance. Actual performance can vary depending on operating conditions. Application and performance data subject to change without notice. All specifications are nominal unless noted otherwise.