

HIGHLIGHTS

- Available in 3000K, 4000K, and 5000K
- Steel Housing + Acrylic Lens
- 120-277 Volt Input
- ETL Approved
- Easy Installation
- Damp Location Rated
- 50,000 Hour Life
- US based Quantum Lighting Technologies Driver & modules


LUXRITE LED



Side View
With Removable
Designer Cover



Plate Cover



MODULE & DRIVER MANUFACTURER WARRANTY

5-Year Life

Based on normal household usage
(3 hours a day/7 days a week) in accordance
with package and bulb directions.

Quantum Lighting Technologies
Ontario, CA 91761



LUXRITE

SPECIFICATIONS

MODEL	FINISH	MERCURY FREE	DAMP LOCATION
ALL	WHITE DIFFUSE PC	●	●

	MODEL	DESCRIPTION	DIMENSION	COLOR TEMPERATURE	LUMENS	CRI	WATT	AVERAGE LIFETIME	VOLTS	LUMEN EFFICACY	ETL	DLC
24"	LR25140	LED24/LINEAR/830/UNV/2	23.25"L*2.6"W*2.5"H	3000K SOFT WHITE	1800	80	17	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
	LR25141	LED24/LINEAR/840/UNV/2	23.25"L*2.6"W*2.5"H	4000K COOL WHITE	1800	80	17	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
	LR25142	LED24/LINEAR/850/UNV/2	23.25"L*2.6"W*2.5"H	5000K BRIGHT WHITE	1800	80	17	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
36"	LR25143	LED36/LINEAR/830/UNV/2	36"L*2.6"W*2.5"H	3000K SOFT WHITE	2650	80	26	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
	LR25144	LED36/LINEAR/840/UNV/2	36"L*2.6"W*2.5"H	4000K COOL WHITE	2650	80	26	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
	LR25145	LED36/LINEAR/850/UNV/2	36"L*2.6"W*2.5"H	5000K BRIGHT WHITE	2650	80	26	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
48"	LR25146	LED48/LINEAR/830/UNV/2	46.5"L*2.6"W*2.5"H	3000K SOFT WHITE	3600	80	34	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
	LR25147	LED48/LINEAR/840/UNV/2	46.5"L*2.6"W*2.5"H	4000K COOL WHITE	3600	80	34	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
	LR25148	LED48/LINEAR/850/UNV/2	46.5"L*2.6"W*2.5"H	5000K BRIGHT WHITE	3600	80	34	50000hrs (45.7yrs)	120-277	105.9	ETL	DLC
96"	LR25152	LED96/LINEAR/840/UNV2	94"L*5"W*3.3"H	4000K COOL WHITE	7040	80	68	30000hrs (27.4yrs)	120-277	104	ETL	
	LR25153	LED96/LINEAR/850/UNV2	94"L*5"W*3.3"H	5000K NATURAL	7040	80	68	30000hrs (27.4yrs)	120-277	104	ETL	

LR25149 Plate Cover

