




52151-N*




52151-MSN*
"MS" bracket for 1½", 2½",
3¾", 4", 6" metal studs




52151-BN*
"B" bracket
mounted flush




52151-VN*
"SV" bracket
mounted flush




52151-CVN*
"CV" bracket
mounted flush




52151-CVNP




52151-X*




52151-XP*




52151-BX*
"B" bracket
mounted flush



52151-VX*
"SV" bracket
mounted flush



52151-CVX*
"CV" bracket
mounted flush



52151-MSX*
"MS" bracket for
1½", 2½", 3¾",
4", 6" metal studs

4" Square Boxes – Continued

Cat. No.	Clamps	Brkts.	Knockouts			Std. Ctn.
			Ea. Side Conduit	Ea. End Cable	Bottom Conduit	
1½" deep—with nonmetallic sheathed cable clamps—21.0 cubic inch capacity						
52151-N**	C-5	—	2-½" 1-½" & ¾"E	2	1-½"	50
52151-MSN**	C-5	MS	2-½" 1-½" & ¾"E	2	1-½"	25
52151-BN**	C-5	B	2-½" 1-½" & ¾"E	2	1-½"	25
52151-VN**	C-5	SV	2-½" 1-½" & ¾"E	2	1-½"	25
52151-CVN**	C-5	CV	2-½" 1-½" & ¾"E	2	1-½"	25
52151-CVNP	C-5	CV	2-½" 1-½" & ¾"E	2	1-½"	25
1½" deep—with armored cable/metal clad clamps—21.0 cubic inch capacity						
52151-X**	C-3	—	2-½" 1-½" & ¾"E	2	1-½"	50
52151-XP**	C-3	—	2-½" 1-½" & ¾"E	2	1-½"	50
52151-BX**	C-3	B	2-½" 1-½" & ¾"E	2	1-½"	25
52151-VX**	C-3	SV	2-½" 1-½" & ¾"E	2	1-½"	25
52151-CVX**	C-3	CV	2-½" 1-½" & ¾"E	2	1-½"	25
52151-MSX**	C-3	MS	2-½" 1-½" & ¾"E	2	1-½"	25

** Per U.L. 514-A, suitable for use without a bonding jumper in circuits above or below 250 volts.

* All Bracketed Boxes come complete with eccentric knockouts.

• Pigtail wire is #12 AWG insulated, 10½" long.