

Bronze

| | | BRON- ZODIC | BANK BRONZE | SATIN BRONZE | STATUARY BRONZE |
|--|---|----------------|----------------|-----------------|--------------------|
| | 9 Blanks (Box Mntg. 3.281") (9B) | 61159 | 65159 | 66159 | 69159 |
| | 10 Blanks (Box Mntg. 3.281") (10B) | 61160 | 65160 | 66160 | 69160 |
| | Block Duplex/GFI Recept. (SRM) | 61401 | 65401 | 66401 | 69401 |
| | 2 Block Duplex/GFI Recepts. (2SRM) | 61402 | 65402 | 66402 | 69402 |
| | 3 Block Duplex/GFI Recepts. (3SRM) | 61403 | 65403 | 66403 | 69403 |
| | 4 Block Duplex/GFI Recepts. (4SRM) | 61404 | 65404 | 66404 | 69404 |
| | 5 Block Duplex/GFI Recepts. (5SRM) | 61405 | 65405 | 66405 | 69405 |
| | 6 Block Duplex/GFI Recepts. (6SRM) | 61406 | 65406 | 66406 | 69406 |
| | 7 Block Duplex/GFI Recepts. (7SRM) | 61407 | 65407 | 66407 | 69407 |
| | 8 Block Duplex/GFI Recepts. (8SRM) | 61408 | 65408 | 66408 | 69408 |
| | 9 Block Duplex/GFI Recepts. (9SRM) | 61409 | 65409 | 66409 | 69409 |
| | 10 Block Duplex/GFI Recepts. (10SRM) | 61410 | 65410 | 66410 | 69410 |
| | One 5/8" ID Phone (Box Mntg. 3.281") (01)* | 61201 | 65201 | 66201 | 69201 |
| | Two 5/8" ID Phones (Box Mntg. 3.281") (02)* | 61202 | 65202 | 66202 | 69202 |
| | One 5/8" ID Phone with Metal Bushing (Box Mntg. 3.281") (61)* | 61591 | 65591 | 66591 | 69591 |
| | One Phone .5" with .375 ID Grommet and Mounting Strap (Device Mntg. 2.375")* | 61181 | 65181 | 66181 | 69181 |
| | One Phone 1.405" with 1" ID Plastic Bushing (Box Mntg. 3.281") (71)* | 61581 | 65581 | 66581 | 69581 |

Material Specifications


| Stainless Steel | Type 302 Spec. Grade (18% chrome-8% nickel) Non-Magnetic and Corrosion Resistant For hospitals, schools and other public institutions. | Finish | Shape | Thickness | U.S. Bureau Standards Symbols | Finish Designator | Cat. Page # |
|-----------------|---|---------------|-------|-----------|-------------------------------|-------------------|-------------|
| | (302SS) | #4 Fine Satin | S | .035 | US #32D | 93000 | A7-13 |
| | (302SS-PRL) | #4 Fine Satin | P | .035 | US #32D | 53000 | A42-47 |
| | (302-6SS) | #4 Fine Satin | S | .060 | US #32D | 70000 | A28-34 |
| | (302SP) | Mirror Polish | S | .035 | US #32 | 68000 | A28-34 |
| | Type 430 (SS) | #4 Fine Satin | S | .030 | US #32 | 97000 | A7-13 |
| | Type 430 (SS-PRL) | #4 Fine Satin | P | .030 | US #32D | 57000 | A42-47 |

| Aluminum | Clear Anodized (5AA) | Matte, Smooth | S | .050 | US #28 | 95000 | A28-34 |
|----------|--------------------------|---------------|---|------|--------|-------|--------|
| | Clear Anodized (5AA-PRL) | Matte, Smooth | P | .050 | US #28 | 55000 | A42-47 |
| | Bright Satin (SAL) | Satin | S | .040 | — | 62000 | A28-34 |

| Brass & Bronze Lacquered to prevent oxidation | Statuary Bronze Dark (4DBR) | Antiqued, Relieved | S | .040 | US #20 | 69000 | A35-41 |
|--|-----------------------------|--------------------|---|------|---------|-------|--------|
| | Bank Bronze Medium (4ABR) | Antiqued, Relieved | S | .040 | US #10B | 65000 | A35-41 |
| | Satin Brass (4BB) | Satin #4 Polish | S | .040 | US #4 | 94000 | A28-34 |
| | Satin Brass (4BB-PRL) | Satin #4 Polish | P | .040 | US#4 | 54000 | A42-47 |
| | Satin Brass (6BB) | Satin #4 Polish | S | .060 | US #4 | 96000 | A28-34 |
| | Satin Bronze (4SBR) | Satin #4 Polish | S | .040 | US #10 | 66000 | A35-41 |
| | Satin Bronze (4SBR-PRL) | Satin #4 Polish | P | .040 | US #10 | 56000 | A42-47 |
| | Polished Brass (4PB) | Mirror Finish | S | .040 | US #3 | 64000 | A28-34 |

| Lexan® Thermoplastic | Brown | 91000 | A54-57 |
|-------------------------|-------|--------|--------|
| | Gray | 77000G | A54-57 |
| | Ivory | 92000 | A54-57 |
| | Red | 77000R | A54-57 |
| | White | 90000 | A54-57 |













Bronze



For color photos of finishes see inside front cover.


STANDARD SHAPE

See page A84 for ordering Custom Plates not found in this listing.


| | BRONZODIC LACQUER ON TYPE 302 STAINLESS (.035") | BANK BRONZE (.040") ANTIQUED & RELIEVED US #10B (4ABR) | SATIN BRONZE (.040") SATIN FINISH US #10 (4SBR) | STATUARY BRONZE (.040") DARK ANTIQUED & RELIEVED US#20 (4DBR) |
|---|---|--|---|---|
|  1 Toggle Switch (1T) | 61071 | 65071 | 66071 | 69071 |
|  2 Toggle Switches (2T) | 61072 | 65072 | 66072 | 69072 |
|  3 Toggle Switches (3T) | 61073 | 65073 | 66073 | 69073 |
|  4 Toggle Switches (4T) | 61074 | 65074 | 66074 | 69074 |
|  5 Toggle Switches (5T) | 61075 | 65075 | 66075 | 69075 |
|  6 Toggle Switches (6T) | 61076 | 65076 | 66076 | 69076 |
|  7 Toggle Switches (7T) | 61077 | 65077 | 66077 | 69077 |
|  8 Toggle Switches (8T) | 61078 | 65078 | 66078 | 69078 |
|  9 Toggle Switches (9T) | 61079 | 65079 | 66079 | 69079 |
|  10 Toggle Switches (10T) | 61080 | 65080 | 66080 | 69080 |
|  1 Duplex Receptacle (10DR) | 61101 | 65101 | 66101 | 69101 |
|  2 Duplex Receptacles (20DR) | 61102 | 65102 | 66102 | 69102 |

WALL PLATE COLOR GUIDE


STANDARD SHAPE




A B C D E



F G H I J K



L M N O P



Q R S T U

- | | | |
|--|--------------------------------|--|
| A. Polished Chrome (83000) | G. Brown Wrinkle (98000) | N. Red Semi-Gloss (51000) |
| B. Stainless Steel (97000, 93000, 70000) | H. White Wrinkle (85000) | O. Aluminum Painted Steel/Cadilite (88000) |
| C. Polished Stainless (68000) | I. Ivory Semi-Gloss (84000) | P. Black Matte (87000) |
| D. Clear Anodized Aluminum (95000) | J. Sprayed Brass Matte (81000) | Q. Satin Brass (94000, 96000) |
| E. Satin Aluminum (62000) | K. White Semi-Gloss (86000) | R. Bank Bronze (65000) |
| F. Ivory Wrinkle (99000) | L. Brown Semi-Gloss (82000) | S. Satin Bronze (66000) |
| | M. Gray Semi-Gloss (58000) | T. Statuary Bronze (69000) |
| | | U. Polished Brass (64000) |