



Energy saving elegance that gives a beautiful sparkle of light

LED B11

Philips LED B11 candles offer energy saving ambiance with the elegant effect of incandescent candles. These designs provides light in an omnidirectional manner, giving lighting designers a long life alternative to standard incandescent sources.

Benefits

Features

Application

Versions





Candelabra Screw B 35mm Clear



Single Contact Medium Screw B 35mm Clear

LED B11

Dimensional drawing



Product	D	C
3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	35 mm	100 mm
5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	35 mm	100 mm

Product	D	C
5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	35 mm	92 mm
3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	35 mm	92 mm

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Voltage (Nom)	120 V
Starting Time (Nom)	0.5 s

General Information

Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X

Light Technical

Color Code	927-922
Color Rendering Index (Nom)	90
Llmf At End Of Nominal Lifetime (Nom)	70 %

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	B11

Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
549568	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	40 W	3.3 W
549337	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	60 W	5.5 W
549584	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	40 W	3.3 W
549345	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	60 W	5.5 W

General Information

Order Code	Full Product Name	Cap-Base
549568	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	E12
549337	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	E12

Order Code	Full Product Name	Cap-Base
549584	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	E26
549345	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	E26

LED B11

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
549568	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	300 lm
549337	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	500 lm

Order Code	Full Product Name	Luminous Flux (Nom)
549584	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	300 lm
549345	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	500 lm

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
549568	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	50 °C
549337	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	60 °C
549584	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	50 °C
549345	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	60 °C

