

DATA/VOICE CABLE

Cat6e -Enhanced Category 6

4 Pair -23 AWG

Twisted Pairs

Direct Burial, Water Block Tape



CONSTRUCTION	
Construction	- Solid Bare copper
Insulation	- High Density Polyethylene (HDPE)
Pairing	- 4 Twisted Pairs
Jacket	- UV resistant low-density Polyethylene (LDPE)

Applications:

- High Speed Horizontal Cabling
- 100 Mbps TPDDI
- 1000 Base T
- 622 Mbps ATM
- IEEE 802.3
- IEEE 802.5
- Digital Video
- Suitable for direct burial

Standards:

- EIA/TIA 568
- ISO/IEC 11801
- ETL/UL Available

Part #	AWG	Pairs	Nom. O.D.	Lbs./M'
J562304-DB	23	4	0.236"	32

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

*Cables are specified with a 5% allowance on propagation delay to the TIA/EIA 568.B.2-1 specification due to waterproofing agents.

COLOR CODE CHART	
Pairs	Color
1	White/Blue Stripe & Blue/White Stripe
2	White/Orange Stripe & Orange/White Stripe
3	White/Green Stripe & Green/White Stripe
4	White/Brown Stripe & Brown/White Stripe