


TYPE SPAR

Features

- Transparent flexible insulating cover
- Range adjustable trim-to-fit tip
- Unique shape and compact design
- Connector, cover and cable tie packaged together
- UL Listed and CSA Certified for 600 volts
- Dual Rated

Benefits

- No taping and allows visual inspection of splice
- Ensures proper fit of cover to cable
- Provides ease of installation, versatility and serviceability of connections made in tight spaces
- Provides ease of ordering
- Ensures reliability
- Use with copper or aluminum conductor



| Catalog Number | Wire Range | Dimensions | | | Screw Size & Shape |
|----------------|-------------|------------|------|------|--------------------|
| | | L | W | H | |
| SPAR-4 | 4-14 | 3.30 | 1.55 | .76 | slotted |
| SPAR-2 | 2-14 | 3.83 | 1.75 | .95 | slotted |
| SPAR-1/0 | 1/0-14 | 4.80 | 1.94 | 1.14 | 3/16" socket head |
| SPAR-250 | 250kcmil-6 | 5.67 | 2.41 | 1.29 | 5/16" socket head |
| SPAR-350 | 350kcmil-10 | 6.17 | 3.29 | 1.79 | 5/16" socket head |
| SPAR-500 | 500kcmil-4 | 7.94 | 3.66 | 2.28 | 3/8" socket head |

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)
Not suitable for direct burial.

DE-OX Oxide Inhibitor is recommended for all aluminum terminations.

Tested to UL 486A/B, UL File E6207