


LED Small Floods

YOKE BRACKET MOUNT - FIXTURE INCLUDES MOUNT



- Lumiled 3030 LEDs
- CCT: 3K, 4K, 5K
- Voltage: 120-277V
- Operating Temp: -40°F To 122°F
- IP65 Wet Location Rated
- 18" Whip
- 50,000+ Hr Life Expectancy
- cULus & DLC Listed
- 5 Year Warranty




FLOOD LIGHTING

CAT. NO.	WATTS	HOUSING COLOR	COLOR TEMP	DELIVERED LUMENS	REPLACES METAL HALIDE	DIMENSIONS (INCHES)				WEIGHT (LBS)	CASE QTY	EACH
						A	B	C	D			
71531A	15	BRONZE	5000K	1,624	70W	4-5/8	3-3/8	4-3/8	1-1/2	1.5	16	
71801A	15	WHITE	5000K	1,624	70W	4-5/8	3-3/8	4-3/8	1-1/2	1.5	16	
74073A	15	BRONZE	4000K	1,603	70W	4-5/8	3-3/8	4-3/8	1-1/2	1.5	16	
71802A	15	BRONZE	3000K	1,593	70W	4-5/8	3-3/8	4-3/8	1-1/2	1.5	16	
71803A	15	WHITE	3000K	1,593	70W	4-5/8	3-3/8	4-3/8	1-1/2	1.5	16	
71532A	30	BRONZE	5000K	3,432	100W	7-1/2	5-1/2	7-1/8	1-5/8	3	8	
71804A	30	WHITE	5000K	3,432	100W	7-1/2	5-1/2	7-1/8	1-5/8	3	8	
74074A	30	BRONZE	4000K	3,404	100W	7-1/2	5-1/2	7-1/8	1-5/8	3	8	
71805A	30	BRONZE	3000K	3,404	100W	7-1/2	5-1/2	7-1/8	1-5/8	3	8	
71806A	30	WHITE	3000K	3,453	100W	7-1/2	5-1/2	7-1/8	1-5/8	3	8	
71533A	50	BRONZE	5000K	5,793	150W	8-1/2	6-1/2	8-1/2	1-7/8	4	6	
71807A	50	WHITE	5000K	5,793	150W	8-1/2	6-1/2	8-1/2	1-7/8	4	6	
74075A	50	BRONZE	4000K	5,778	150W	8-1/2	6-1/2	8-1/2	1-7/8	6.4	6	
71808A	50	BRONZE	3000K	5,717	150W	8-1/2	6-1/2	8-1/2	1-7/8	6.4	6	
71809A	50	WHITE	3000K	5,717	150W	8-1/2	6-1/2	8-1/2	1-7/8	6.4	6	

LED Small Floods

1/2" KNUCKLE MOUNT
FIXTURE INCLUDES MOUNT



CAT. NO.	WATTS	HOUSING COLOR	COLOR TEMP	DELIVERED LUMENS	REPLACES METAL HALIDE	DIMENSIONS (INCHES)				WEIGHT (LBS)	CASE QTY	EACH
						A	B	C	D			
71551A	15	BRONZE	5000K	1,624	70W	5-3/8	4-3/8	4-3/8	1-1/2	1.5	16	
71821A	15	WHITE	5000K	1,663	70W	5-3/8	4-3/8	4-3/8	1-1/2	1.5	16	
74076A	15	BRONZE	4000K	1,603	70W	5-3/8	4-3/8	4-3/8	1-1/2	1.5	16	
71552A	15	BRONZE	3000K	1,566	70W	5-3/8	4-3/8	4-3/8	1-1/2	1.5	16	
71553A	15	WHITE	3000K	1,566	70W	5-3/8	4-3/8	4-3/8	1-1/2	1.5	16	
71554A	30	BRONZE	5000K	3,718	100W	9-1/8	7-7/8	7-1/8	1-5/8	3	8	
71822A	30	WHITE	5000K	3,718	100W	9-1/8	7-7/8	7-1/8	1-5/8	3	8	
74077A	30	BRONZE	4000K	3,427	100W	9-1/8	7-7/8	7-1/8	1-5/8	3	8	
71555A	30	BRONZE	3000K	3,453	100W	9-1/8	7-7/8	7-1/8	1-5/8	3	8	
71556A	30	WHITE	3000K	3,453	100W	9-1/8	7-7/8	7-1/8	1-5/8	3	8	
71557A	50	BRONZE	5000K	6,179	150W	10-1/8	8-1/8	8-1/2	1-7/8	4	6	
71823A	50	WHITE	5000K	6,179	150W	10-1/8	8-1/8	8-1/2	1-7/8	4	6	
74078A	50	BRONZE	4000K	5,778	150W	10-1/8	8-1/8	8-1/2	1-7/8	4	6	
71824A	50	BRONZE	3000K	5,882	150W	10-1/8	8-1/8	8-1/2	1-7/8	4	6	
71825A	50	WHITE	3000K	5,882	150W	10-1/8	8-1/8	8-1/2	1-7/8	4	6	