

Conduit Beam Clamps

For Threaded Rigid Conduit

Application:

Provides support for conduit hanging systems.

Features:

- Steel bolt - case hardened
- Standard Sizes 1"-2 1/2"
Jaw Opening 3/4"-1 1/4"

Standard Materials:

Malleable Iron/Steel Bolt-Case Hardened

Standard Finish:

Zinc Plated

Application:

Clamp on to structure member to provide mounting means for the attachment of conduit hangers either directly or by means of threaded rod.

Standard Materials:

Steel

Standard Finish:

Zinc Plated

Application:

For terminating end of jack chain, used to suspend lighting fixtures, etc.

Standard Materials:


Steel

Standard Finish:

Zinc Plated



Type 620



CATALOG NUMBER	TRADE SIZE	TAP SIZE	JAW OPENING	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100	NAED MFG #78-5994 UPC/DCI #
620	1"	1/4" - 20"	0.750	1.125	1.400	1.385	25	250	22	16201
621	1"	3/8" - 16"	0.750	1.125	1.400	1.385	25	250	22	16211
625	2"	3/8" - 16"	0.875	1.990	1.755	1.885	-	50	90	16251
626	2"	1/2" - 13"	0.875	1.990	1.755	1.885	-	25	90	16261
627	2-1/2"	1/2" - 13"	1.250	2.530	2.140	2.500	-	25	160	16271


Loading Capacity

CATALOG NUMBER	TRADE SIZE	WORKING LOAD	TEST LOAD FOR 5 MIN.
620	1"	250 LBS	750 LBS
621	1"	250 LBS	750 LBS
625	2"	500 LBS	1500 LBS
626	2"	500 LBS	1500 LBS
627	2-1/2"	500 LBS	1500 LBS

Insulator Supports



Type S620



CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
S620	1/4" - 20"	0.920	1.400	1.625	25	250	15	16207

S Hooks



Type 224

CATALOG NUMBER	TRADE SIZE	UNIT PACK	STANDARD PACK	WEIGHT (LBS.) PER 100 PCS.	NAED MFG #78-5994 UPC/DCI #
224	#12	-	1000	5	83247
225	#10	-	1000	9	83257