

### Merchandising System for D-PAK® Products

#### Applications


- Dry-tite® boxes and covers protect wiring devices, switches, electronic components and terminal blocks in Dry, Damp and Wet Locations
- Junction for branch conduits
  - “A” Series bodies for Rigid and Intermediate Metal Conduit (IMC) conduit maintain a weather resistant conduit system when used with covers and gaskets
  - “B” Series bodies for thin wall conduit Electrical Metallic Tubing (EMT) saves cost of connector and labor in indoor applications
- Accessible wiring chamber provides a convenient location to maintain or change a system, pull conductors and make splices



DIH3-1-LM



DALB



DCCD



D2L80S3

#### Features/Benefits

- Combination packaging of conduit body, cover and gasket reduces handling and inventory costs
- Selection of colored finishes — silver, bronze and white — match most widely used finishes in commercial and residential construction
- Reduced quantities in easy-to-store cartons. Saves labor and handling, reduces error and handling costs
- Bar coding on carton and product
- See-through wrapper provides instant identification and protects product on job site
- Easy to read labels speeds selection, handling and storage.

#### Standard Materials


- Refer to appropriate section in this catalog

#### Standard Finish

- Powder coated finish
- Colors — Silver, Bronze & White

#### Compliances

- UL® Listed
- CSA Certified
- Federal Spec. W-C-586








The Merchandising System for D-PAK® Products Attracts Attention with Bold Graphics and Encourages Self-Service with Clean, Easy-to-Read Labels.

- Bold red, black, and white descriptive merchandising labels
- Labor saving 2-piece carton
- Combination pack of conduit body, cover and gasket
- Choice of finish: silver, bronze or white
- English, Spanish and French instructions
- Protective see-through wrap




### Conduit Bodies with Covers and Gaskets




	CAT. NO.	CAT. NO.	HUB SIZE
<b>Through Feed</b>			
	RIGID IMC (RAINTIGHT)	EMT	
	DAC-1-CG	—	1/2"
	DAC-2-CG	—	3/4"
	DAC-3-CG	—	1"
<b>Back Opening</b>			
	DALB-1-CG	DBLB-1-C•	1/2"
	DALB-2-CG	DBLB-2-C•	3/4"
	DALB-3-CG	DBLB-3-C•	1"
	DALB-4-CG	—	1 1/4"
	DALB-5-CG	—	1 1/2"
	DALB-6-CG	—	2"
<b>Left Side Opening</b>			
	DALL-1-CG	—	1/2"
	DALL-2-CG	—	3/4"
	DALL-3-CG	—	1"
<b>Right Side Opening</b>			
	DALR-1-CG	—	1/2"
	DALR-2-CG	—	3/4"
	DALR-3-CG	—	1"
<b>T-Style</b>			
	DAT-1-CG	—	1/2"
	DAT-2-CG	—	3/4"
	DAT-3-CG	—	1"

- Body and cover only


### Service Entrance Bodies

	CAT. NO.	HUB SIZE
<b>Back Opening</b>		
	DASLB-1	1/2"
	DASLB-2	3/4"
	DASLB-3	1"


### Boxes

	CAT. NO.	HUB SIZE	COLOR	OUTLETS
<b>Single Gang — with Mounting Lugs, 2 Plugs and Ground Screw</b>				
<b>Three Outlets</b>				
	DIH3-1-LM	1/2"	Silver	Top 1
	DIH3-1-LM-BR	1/2"	Bronze	Bottom 1
	DIH3-1-LM-WH	1/2"	White	Back 1
	DIH3-2-LM	3/4"	Silver	
	DIH3-3-LM	1"	Silver	Total 3
<b>Four Outlets</b>				
	DIH4-2-LM	1/2"	Silver	Top 2
	DIH4-1-LM-BR	1/2"	Bronze	Bottom 1
	DIH4-1-LM-WH	1/2"	White	Back 1
	DIH4-2-LM	3/4"	Silver	Total 4
<b>Five Outlets</b>				
	DIH5-1-LM	1/2"	Silver	Top 2
	DIH5-2-LM	3/4"	Silver	Bottom 2
				Back 1
			Total 5	


### Four Outlets

	DIH4-2-LM	1/2"	Silver	Top 2
	DIH4-1-LM-BR	1/2"	Bronze	Bottom 1
	DIH4-1-LM-WH	1/2"	White	Back 1
	DIH4-2-LM	3/4"	Silver	Total 4


### Five Outlets

	DIH5-1-LM	1/2"	Silver	Top 2
	DIH5-2-LM	3/4"	Silver	Bottom 2
				Back 1
			Total 5	

### Two Gang — with Mounting Lugs, 2 Plugs and Ground Screw

<b>Three Outlets</b>				
	D2IH3-1	1/2"	Silver	Top 1
				Bottom 1
				Back 1
				Total 3

### Round — with Cast Mounting Lugs, 4 Plugs and Ground Screw


<b>Five Outlets</b>				
	DS-47	1/2"	Silver	Side 4
	DS-47-BR	1/2"	Bronze	Bottom 1
	DS-47-WH	1/2"	White	
	DS-48	3/4"	Silver	
	DS-48-BR	3/4"	Bronze	
DS-48-WH	3/4"	White	Total 5	

- Body and cover only.

### Device Covers

CAT. NO.	COLOR	DESCRIPTION
----------	-------	-------------

#### Duplex Receptacle Cover, Horizontal




DCCD	Silver	Device mount
DCCD-BR	Bronze	
DCCD-WH	White	

#### Duplex Receptacle Cover, Vertical



DCCDV	Silver	Device mount
DCCDV-BR	Bronze	
DCCDV-WH	White	

#### GFCI Receptacle Cover, Horizontal



DCCG	Silver	Device mount
DCCG-BR	Bronze	
DCCG-WH	White	

#### GFCI Receptacle Cover, Vertical



DCCGV	Silver	Device mount
DCCGV-BR	Bronze	
DCCGV-WH	White	

### Blank Covers


CAT. NO.	COLOR	DESCRIPTION
----------	-------	-------------

#### Single Gang



DCCB	Silver	Device mount
DCCB-BR	Bronze	
DCCB-WH	White	

#### Two Gang



D2CCB	Silver	Device mount
-------	--------	--------------

#### Round



DCCRB	White	5" round cover with mounting holes 3½" on center (not Raintight)
-------	-------	--

### Lampholders

CAT. NO.	COLOR	DESCRIPTION
----------	-------	-------------

#### Standard



DL-80	Silver	Inside gasket and ground screw, 150W PAR 38 Max. lamp
DL-80-BR	Bronze	
DL-80-WH	White	

#### Floodlight




D2L80S3	Silver	Two lampholders and cover with three ½" holes, gasket, screws and plug
---------	--------	--

### Lampholder Cover

CAT. NO.	HUB SIZE	COLOR	DESCRIPTION
----------	----------	-------	-------------

#### Single Gang



DLC-31	½"	Silver	Three ½" holes, supplied with gasket, screws and plug
DLC-31-BR	½"	Bronze	
DLC-31-WH	½"	White	

#### Round



DSS-1	½"	Silver	Device mount with gasket, screws and plug
DSS-1-BR	½"	Bronze	
DSS-1-WH	½"	White	
DSS-3	½"	Silver	
DSS-3-BR	½"	Bronze	
DSS-3-WH	½"	White	

### Plugs

CAT. NO.	HUB SIZE	COLOR
----------	----------	-------



DPLG-1	½"	Silver
DPLG-1-BR	½"	Bronze
DPLG-1-WH	½"	White
DPLG-2	¾"	Silver

### Traditional 2 Lamp Round Box Kit



CS212

CAT. NO.	COLOR
CS212	Silver
CS212BR	Bronze
CS212WH	White

### Contemporary 2 Lamp Round Box Kit



CS228

CAT. NO.	COLOR
CS228	Silver
CS228BR	Bronze
CS228WH	White

### Duplex Weatherproof Outlet Device Kit



CS312

CAT. NO.	COLOR
CS312	Silver
CS312BR	Bronze
CS312WH	White

### GFCI Weatherproof Outlet Device Kit



CS315

CAT. NO.	COLOR
CS315	Silver

### Contemporary Stake Light with Cord



CS780BR

CAT. NO.	COLOR
CS780BR	Bronze

### Traditional 2 Lamp, Round Box with Photocell Kit



CS902

CAT. NO.	COLOR
CS902	Silver
CS902BR	Bronze
CS902WH	White

### D-PAK® Kits not shown

CAT. NO.	DESCRIPTION	COLOR
CSNMG	Single gang, non-metallic, while-in-use weatherproof kit includes CKNM cover, box and GFCI receptacle	Clear Cover
CSMGV	Single gang, metallic, vertical GFCI, while-in-use. Weatherproof kit includes CKMGV cover, box and GFCI receptacle	Silver

Red•Dot® Weatherproof Boxes and Covers