


Dimensions / Data

48" x 48" PG Style Polymer Concrete (Stackable) Assembly

Hex Head Bolts are Standard



Covers

DESCRIPTION	TIER	DESIGN / TEST LOAD #	WEIGHT #	PALLET QTY	PART NO.
Lightweight 4 Bolts	5	5,000 / 7,500	286	10	LG4848CA00**
W/ 4 Bolts	15	15,000 / 22,500	364	10	PG4848HA00**
W/ 4 Bolts	22	22,500 / 33,750	596	10	PG4848HH00**
Lightweight No bolts	5	5,000 / 7,500	286	10	LG4848WA00**

Replace ** with a logo code found on page 60. See page 65 for meter and touch/radio read cover options.

Boxes

DESCRIPTION	DEPTH	TIER	DESIGN / TEST LOAD #	WEIGHT #	PALLET QTY	PART NO.
Standard Open Bottom	36"	22	22,500 / 33,750	629	2	PG4848BA36
	48"		22,500 / 33,750	866	2	PG4848BA48
Solid Bottom	36 1/2"	22	22,500 / 33,750	663	2	PG4848DA36
	48 1/2"		22,500 / 33,750	940	2	PG4848DA48

To order boxes with 2 standard mouseholes, replace the letter "A" with the letter "B".