

# MIGHTYLITE

## HIGH POWERED LED FLOODLIGHT



**Extremely powerful, LED floodlights which deliver up to 17,000 lumens of light and can be wired to operate on 25%, 50%, 75% or 100% power as required.**

The 120W and 200W MightyLite Power House floodlights are the latest development in high quality professional floodlighting. They deliver industry-leading levels of light from their high powered Epistar LEDs, and dedicated driver units.

The unit comes with a stainless steel, painted U bracket allowing easy installation and adjustment. It is also supplied with a pipe bracket attachment so the light can be securely fixed to pipes or poles.

✓ **Powerful, professional grade LED floodlights**

Generates up to 100 Lumens per Watt

✓ **Powered by British designed Quad driver**

Enabling the light to be wired so it can use any or all of its 4 separate light units to operate on 25%, 50%, 75% or 100% light level as required

✓ **Versatile installation**

Supplied with stainless steel U bracket and pipe bracket for flexible installation

✓ **High quality, stylish design**

Polycarbonate fascia and light diffusing frosted lens mounted on a die-cast aluminium body

✓ **Weatherproof**

IPX6 rating and works in temperatures from -40°F to +176°F

✓ **Fully certified**

ETL, RoHS, LVD approvals and ERP compliant

### SPECIFICATIONS

Model No:	MITY22091	MITY22031
Lumens:	12,000Lm	17,000Lm
Wattage:	120W	200W
Power Factor:	>0.9	>0.9
Voltage:	110V AC	110V AC
Color Temp:	5400K	5400K
Efficiency:	<80%	<80%
LED Array:	96 LEDs	168 LEDs
Lens:	Frosted	Frosted
Operating Temp:	-40°F to +176°F	-40°F to +176°F
IP Rating:	IPX6	IPX6
Product Size:	8.4"(h) x 12.6"(w) x 3.9"(d)	8.4"(h) x 12.6"(w) x 3.9"(d)