



MUSTANG

TRADITIONAL
Wall Lights

- USA Manufacturing at Import Prices
- Rugged traditional aluminum die-cast housing
- Lifespan: 100,000 hours
- Lens assembly is designed to provide high efficiency and to target the light where needed
- Installation: Fixture retains the same knock-out sizes and positions as previous models, reducing wiring costs



20 Watt LED Wall Light



AWT20LED

19 Input Watts
110 LpW Efficacy
2,133 Total Lumens
4500K Color Temperature
84 Color Rendering Index

30 Watt LED Wall Light



AWS30LED

30 Input Watts
129 LpW Efficacy
3,769 Total Lumens
4500K Color Temperature
83 Color Rendering Index

40-60-80 Watt LED Wall Light



AWM40LED

43 Input Watts
133 LpW Efficacy
5,805 Total Lumens
4500K Color Temperature
83 Color Rendering Index

AWM60LED

62 Input Watts
128 LpW Efficacy
7,871 Total Lumens
4500K Color Temperature
82 Color Rendering Index

AWM80LED

79 Input Watts
129 LpW Efficacy
10,120 Total Lumens
4500K Color Temperature
83 Color Rendering Index

