

QUOIZEL®

Artisans in Lighting…since 1930

2016 – 2017

MAIN CATALOG 2016-17

QUOIZEL.

Artisans in Lighting...since 1930

Welcome!

Our newest catalog is full of decorative lighting designed to help you enhance the beauty of your home. Our design team has been hard at work, and we hope that you enjoy our newest creations.

LED is the most exciting technology to impact Quoizel products. Its increased lumen output, energy efficiency and long life are three of the top benefits. As a result, the vast majority of our products are LED compatible and many of our new outdoor and bath fixtures now come with an integrated LED light source or LED bulbs. Check the product descriptions for specific information.

On behalf of the entire Quoizel family, thank you for making our products part of your home.

Sincerely,

Rick Seidman
President / CEO

QUOIZEL

Since 1930, Quoizel has made it a practice to keep in step with evolving fashion trends in home décor and interior design around the world.

As an industry leader in home lighting for over 80 years, we at Quoizel repeatedly offer successful product lines ranging in style from traditional to contemporary, keeping hand-crafted artistry, cutting-edge innovation and enduring quality at our very core.

Our Board of Directors

Rick Seidman
President & CEO

Ira Phillips
Chairman of the Board

Toni Phillips
Executive Vice President

Todd Phillips
Executive Vice President

Ed Clark
Senior Vice President



Tim Hensch
Vice President/Operations

Our Locations

Charleston, SC

Hauppauge, NY

Follow **QUOIZEL** on social media:

Scan with your smart phone or tablet to view informative videos relating to our product line and catalog!

Artisans at WORK

Guide to icons & reference codes

TRUCK ITEM

TITLE 20 COMPLIANT

All portable lamps shipped into the state of California will contain an energy-efficient fluorescent light bulb.

TITLE 24 COMPLIANT ENERGY-EFFICIENT

- 13W, 18W or 23W Compact Fluorescent Included
- CFL Spring Self-Ballasted GU 24

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying this logo. (Medium base bulbs only)

FIXTURE EXCEEDS 50 POUNDS

DIFFUSER INCLUDED

DAMP LOCATION

WET LOCATION

MOUNTS AS UPLIGHT OR DOWNLIGHT

MOUNTS VERTICALLY OR HORIZONTALLY

ADA APPROVED

DIMMERS:

Integrated Low Voltage LED Fixture – requires Electronic Low Voltage (ELV) dimmer.
Integrated 120v LED Fixture – C·L Dimmers recommended.

For more specific dimmer information, please contact: engineering@quoizel.com.

WARRANTY:

Please refer to Quoizel.com for complete warranty information.

Bulbs:

- Bulbs not included unless otherwise noted.
- Vintage Bulbs supplied are not necessarily the maximum wattage allowed.
- Products using LED and Halogen bulbs come with bulb(s) supplied in carton.
- Wattages stated are the maximum recommended; however, you may use lower wattages to suit your lighting needs.

LED:

- Integrated LED information chart provided wherever applicable.

Chain:

- (Single Tier) Chandelier, Dinette, Mini Chandeliers, Pendants, Mini Pendants and Island Lights come with 8' of wire and 4' of chain.
- (Two & Three Tier) Chandeliers and Foyer Fixtures come with 12'of wire and 8' of chain.
- All Outdoor Hanging Fixtures come with 12' of wire and 8' of chain.
- All Chain-Hung Mini Pendants come with 8' of wire and 4' of chain.

Other:

- All Rod-Hung Mini Pendants come with a minimum of 8' of wire.
- All Cord-Hung Mini Pendants come with a minimum of 8' of cord.
- All Cable-Hung Mini Pendants come with a minimum of 8' of cable.

Damp / Wet Locations:

- All flush and semi-flush mounted fixtures, bath fixtures and chandeliers are "Damp Location" listed.
- All outdoor hanging fixtures are "Damp Location" listed.
- All outdoor wall and post lights are "Wet Location" listed.

Electrical:

- All electrical fixtures are rated at 120-volt AC unless otherwise noted.
- Unless specified, all electrical fixtures are cUL or ETL listed.

Hardware:

- Backplate information and HCWO (Height from Center of Wall Opening) included for most wall fixtures (including outdoor) and bath fixtures.
- Canopy information included on almost all fixtures.
- All mirrors come with mounting hardware.

Tiffany / Naturals:

- Glass color in Tiffany lighting products vary in color. No two pieces are identical.
- Products that use natural materials are perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.

Glass / Shades:

- Will appear darker when not illuminated.

In our efforts to constantly improve our products, changes may be made throughout the year that vary from printed information in the catalog.

© Copyright ❖ Patent Number ◆ Patent Pending

Contents

COLLECTIONS

Adonis 38
Baroness 40
Brook Hall 42
Buchanan 44
Downtown 46
Duchess 52
Dury 58
Emery 61
Kendra 64
Kyle 68
La Parra 74
Marquette 78
Monterey Mosaic 81
Taylor 87
Trilogy 92
Whitney 96

MINI-COLLECTIONS

Adams 102
Alexandria 104
Eastvale 105
Chamber 106
Armelle 108
Baron 110
Castile 111
Milbank 112
Grant 114
Laila 116
Metropolis 117
New England 118
Tavern 120
Palmer 122
Remi 123
Odell 124
Opera 126
Noble 128
Sophia 130
New Harbor 133
Wilder 134
Tricia 136
Union Station 138

ADDITIONAL PRODUCTS & ACCESSORIES

Red number represents the category's appearance in our Photo Index immediately following this page.
Black number represents actual appearance in catalog.

Dining & Foyer and More 8, 141
The Platinum Collection 10, 172
Designer Showcase:
Carolyn Kinder 12, 207
UPTOWN / Sergio Orozco 12, 216
Quoizel Naturals 13, 227
Island Lights 15, 253
Pendants 16, 263
Mini Pendants 18, 278
Semi-Flush Mounts 20, 287
Flush Mounts 23, 302
Track Lighting 24, 311
Wall Fixtures 25, 317
Bath Fixtures 26, 321
Outdoor Fixtures 29, 371
Tiffany 31, 459
Table & Floor 33, 507
Mirrors 36, 527
Accessories 534
Full Product Index 538

Collections

Adonis (ADS) 38-39

Baroness (BNS) 40-41

Brook Hall (BKH) 42-43

Buchanan (BCN) 44-45

Downtown (DW) 46-51

Duchess (DH) 52-57

Dury (RDY) 58-60

Emery (ER) 61-63

Kendra (KD) 64-67

Kyle (KY) 68-73

La Parra (LP) 74-77

Marquette (MQ) 78-80

Monterey Mosaic (MY) 81-86

Taylor (TY) 87-91

Trilogy (TRG) 92-95

Whitney (WHI) 96-100

Mini-Collections

Adams (ADA) 102-103

Alexandria (AX) 104

Eastvale (EVE) 105

Chamber (CHB) 106-107

Armelle (AME) 108-109

Baron (BRO) 110

Castile (CS) 111

Milbank (MBK) 112-113

Grant (GRT) 114-115

Laila (LLA) 116

Metropolis (MTP) 117

New England (NA) 118-119

Tavern (TVN) 120-121

Palmer (PLR) 122

Remi (REM) 123

Odell (ODL) 124-125

Opera (OPA) 126-127

Noble (NBE) 128-129

Sophia (SPH) 130-132

New Harbor (NHR) 133

Wilder (WLR) 134-135

Tricia (TCA) 136-137

Union Station (UST) 138-140

Dining & Foyer

Auburn (ABN) 142-144

Mirren (MRN) 145

Castle Hill (CTH) 146-147

Voyager (VYR) 148-149

Carrabelle (CRE) 150-151

Wesley (WSY) 152-153

Estate (EST) 154

Dunn (DUN) 155

Woodrow (QF) 155

Silhouette (SLT) 156

Belhaven (BHN) 157

Alston (QMC) 158-159

Majesty (MJY) 159

Miramar (MMR) 159

Bandelier (BDR) 160

Wyndmoor (WDM) 160

Capri (CP) 160

Ridge Manor (QF) 161

Collins (QF) 161

Frontier (FTR) 161

Celestial (CLT) 162

Kemper (KPR) 162

Amelia (AML) 162



Serenity (SER) 163

Majestic (MJT) 164-165

PHOTO INDEX

Holbrook (HK) 166

Planter (QF) 166



Thornhill (THL) 167

Menlo (MNO) 167

Lakeside (LKE) 168

Colton (CTO) 168

Grand Court (GCT) 168

Sabrina (SRA) 169

Kayden (KDN) 169

Unison (UNS) 169

Pembroke (PB) 170

Burgess (BGS) 170

Anchor (ANR) 171

Knotting (QF) 171

Platinum Collection

Bordeaux (BRX) 174-177

Galaxy (PCGX) 178

Countess (PCCT) 179

Alexa (PCAX) 179

Crowne (PCCR) 180

Crystal Leaf (PCCF) 180

Arena (PCAN) 180

Mercury (PCMY) 181

Treasure (PCTS) 181

Shimmer (PCSR) 181

Vision (PCVN) 182

Paragon (PRN) 182

Highrise (PCHE) 183

Janelle (PCJL) 183

Ella (PCEL) 184

Superior (PCSP) 184

Valla (VLA) 185

Ribbons (RBN) 186-189

Abode (PCAE) 190-191

Array (PCAY) 190

Stellar (PCSL) 192

Encompass (PCEC) 192

Paragon (PRN) 193



Shimmer (PCSR) 194

Alexa (PCAX) 195

Endless (PCED) 195

Evermore (EME) 196-197

Pierre (PCPR) 198

Royale (RYE) 198

Seaview (PCSW) 199

Serena (PCSA) 200

Lacombe (PCLC) 201

Mirabella (PCMR) 201

Divine (PCDV) 202

Dash (PCDH) 203

Glacial (PCGL) 203

Valiant (PCVT) 204

Blade (PCBD) 204

Pace (PCPC) 205

Promenade (PCPE) 205

Bram (PCBM) 206

Carolyn Kinder

Confetti (CKCF) 208-209

Metro (CKMO) 210-211

Sanctuary (CKSC) 212

Brookmont (CKBT) 212

Hickman (CKHM) 212

Ultra (CKUT) 212

Marisol (CKMS) 213

Kendrick (CKKD) 215

Nikos (CKNK) 215

Gaston (CKGN) 215

Sonia (CKSN) 215

Uptown by Sergio Orozco

East Village (UPEV) 216-217

Theater Row (UPTR) 218

Ritz (UPRZ) 219

Carnegie (UPCN) 220-221

Madison Manor (UPMM) 222-223

Columbus Circle (UPCC) 224

Fulton (UPFT) 224

Penn Station (UPPS) 225

Seaport (UPSE) 226

Holita (UPHL) 226

Kendra (KD) 64-67

Kyle (KY) 68-73

Monterey Mosaic (MY) 81-86

Chamber (CH) 106-107

Armelle (AME) 108-109

Baron (BRO) 110

Castile (CS) 111

Tavern (TVN) 120-121

Odell (ODL) 124-125

Auburn (ABN) 142-144

Belhaven (BHN) 157

Wyndmoor (WDM) 160

Holbrook (HK) 166

Planter (QF) 166

Kayden (KDN) 169

Pembroke (PB) 170

Anchor (ANR) 171

Laguna (MCLG) 228-232

Prism (MC) 233

Alistar (MCAL) 233

San Gabriel (NX) 234

Cyrus (MCCS) 234

Kingsford (MCKD) 235

Morrow (MC) 235

Vega (MC) 236

Naturals

Pearce (PER) 236

Belfair (MCBF) 237

Highland (MC) 237

Bandelier (BDR) 238

Tartan (MC) 238

Whispering Wood (AG) 238

Zen (ZE) 239

Arcadia (AI) 240

Zephyr (ZP) 240

Aristocrat (AS) 241

Pomez (TF) 242-243

Captiva (SSCV) 244

Floret (SSFT) 244

Sanibel (SSSB) 245

Flower Field (JD) 245

Kayden (KDN) 280

Alexandria (AX) 254

Brook Hall (BKH) 254


Laguna (MCLG) 254

Adonis (ADS) 255

Emery (ER) 255

Eastvale (EVE) 256

Tavern (TVN) 256-257

New Harbor (NHR) 256

Confetti (CKCF) 258

Marisol (CKMS) 258

Duchess (DH) 259

LaParra (LP) 259


Kyle (KY) 260

Deluxe (DX) 261

Taylor (TY) 261

Remi (REM) 261

Asheville (TFAS) 262

Belle Fleur (TFBF) 262

Inglenook (TFIK) 262

Pendants

Adonis (AD) 39

Baroness (BN) 41

Buchanan (BCN) 45

Downtown (DW) 51

Duchess (DH) 54

Dury (RDY) 60

Emery (ER) 62

Kendra (KD) 67

Kyle (KY) 72

Monterey Mosaic (MY) 84

Trilogy (TRG) 94

Adams (ADA) 103

Alexandria (AX) 104

Eastvale (EVE) 105

Milbank (MBK) 113

Grant (GRT) 115

Metropolis (MTP) 117

Palmer (PLR) 122

Odell (ODL) 125

Wilder (WLR) 134

Bordeaux (BRX) 174

Galaxy (PCGX) 178

Arena (PCAN) 180

Crystal Leaf (PCCF) 180

Mercury (PCMY) 181

Vision (PCVN) 182

Janelle (PCJL) 183

Superior (PCSP) 184

Valla (VLA) 185

Ribbons (RBN) 186-189

Abode (PCAE) 190

Encompass (PCEC) 192

Confetti (CKCF) 208-209

Metro (CKMO) 210

Marisol (CKMS) 213

Fulton (UPFT) 224

Penn Station (UPPS) 225

Laguna (MC) 228

Morrow (MC) 235

Kingsford (MCKD) 235

Belfair (MCBF) 237

Bandelier (BDR) 238

Zen (ZE) 239

Arcadia (AI) 240

Aristocrat (AS) 241

Orion (ON) 264

Jarvis (JV) 265

Amelia (AML) 265

Portland (PTD) 266-267

Brown Lattice (BWL) 267

Pendants

Capri (CP) 268

Bound (BND) 268

Railway (RLY) 268

Mirage (MIR) 269

Jolene (JLE) 269

Cody (CDY) 270

Morroco (QF) 270

Cloverdale (CRA) 271

Long Beach (LBH) 271

Tiffany- many styles available
See section starting on p.459

Mini-Pendants

Adonis (AD) 39

Baroness (BNS) 40

Downtown (DW) 51

Duchess (DH) 56

Dury (RDY) 60

Emery (ER) 62

Kendra (KD) 67

Kyle (KY) 73

La Parra (LP) 76

Monterey Mosaic (MY) 86

Trilogy (TRG) 94

Eastvale (EVE) 105

Grant (GRT) 115

Metropolis (MTP) 117

New England (NA) 119

Sophia (SPH) 132

Wilder (WLR) 135

Union Station (UST) 140

Treasure (PCTS) 181

Ribbons (RBN) 187-189

Confetti (CKCF) 209

Sonia (CKSN) 215

Gaston (CKGN) 215

Kendrick (CKKD) 215

Nikos (CKNK) 215

Penn Station (UPPS) 225

Laguna (MC) 232

Kingsford (MCKD) 235

Pomez (TF) 243

Morroco (QF) 279

Garrison (QPP) 279

Brown Lattice (BWL) 280

Cody (CDY) 280

Ferndale (FE) 280

Kayden (KDN) 280

Mini-Pendants

Steadman (SDN) 281

Marine (MRE) 281

Ridley (QPP) 281

Dublin (DBN) 282

Antero (QPP) 282

Valentina (QPP) 282

Railway (RLY) 283

Highgate (QPP) 283

Tiffany- many styles available
See section starting on p.459

Semi-Flush Mounts

Baroness (BNS) 41

Brook Hall (BKH) 42

Buchanan (BCN) 45

Downtown (DW) 51

Duchess (DH) 56

Dury (RDY) 60

Kendra (KD) 67

Kyle (KY) 72

Monterey Mosaic (MY) 85

Taylor (TY) 90

Trilogy (TRG) 95

Whitney (WHI) 100

Baron (BRO) 110

Castile (CS) 111

Milbank (MBK) 113

Metropolis (MTP) 117

Tavern (TVN) 120

Palmer (PLR) 122

New Harbor (NHR) 133

Wilder (WLR) 135

Union Station (UST) 140

Alexa (PCAX) 179

Crowne (PCCR) 180

Shimmer (PCSR) 181

Vision (PCVN) 182

Superior (PCSP) 184

Array (PCAY) 190

Abode (PCAE) 190

Confetti (CKCF) 209

Metro (CKMO) 210

Marisol (CKMS) 213

Theater Row (UPTR) 218

Penn Station (UPPS) 225

Laguna (MC) 228

Kingsford (MCKD) 235

Semi-Flush Mounts

Pearce (PER) 236

Belfair (MCBF) 237

Zen (ZE) 239

Arcadia (AI) 240

Aristocrat (AS) 241

Sanibel (SSSB) 245

Brown Lattice (BWL) 288

Burgess (BGS) 288

Frontier (FTR) 288

Norwood (QF) 289

Celestial (CLT) 289

Waverly (WV) 290

Cloverdale (CRA) 290

Deluxe (DX) 290-291

Sailor (SLR) 292

Calvary (QF) 292

Ashland (QF) 293

Ozark (OZ) 293

Griffin (GF) 294-295

Jolene (JLE) 296

Majesty (MJY) 296

Mirage (MIR) 296

Cody (CDY) 297

Warren (QF) 297

Belcourt (QF) 297

Castle (QF) 297

Tiffany - many styles available
See section starting on p.459

Flush Mounts

Adonis (ADS) 39

Monterey Mosaic (MY) 85

Chamber (CHB) 106

Laila (LLA) 116



Opera (OPA) 127

Bordeaux (BRX) 175-176

Countess (PCCT) 179

Paragon (PRN) 182

Highrise (PCHE) 183

Ella (PCEL) 184

Valla (VLA) 185

Ribbons (RBN) 187, 189

Laguna (MCLG) 229

Zen (ZE) 239

Melon (ML) 302

Manor (MNR) 303

Summit (SMT) 304

Griffin (GF) 305

Ozark (OZ) 306

Wilson (WLS) 307

Bound (BND) 307

Tiffany - many styles available
See section starting on p.459

Track Lighting

Duchess (DH) 312

Kyle (KY) 312

Monterey Mosaic (MY) 312

Pacifica (PF) 313

Denning (QTR) 313

Eastvale (EVE) 313

Asheville (TFAS) 315

Inglenook (TFIK) 315

Victory (TFVY) 315

Taylor (TY) 316

Wall Lighting

Adonis (ADS) 38

Downtown (DW) 49

Duchess (DH) 57

Kendra (KD) 65

Kyle (KY) 73

La Parra (LP) 76

Marquette (MQ) 79

Montrerey Mosaic (MY) 86

Taylor (TY) 91

Trilogy (TRG) 95

Whitney (WHI) 97

Adams (ADA) 103

Armelle (AME) 109

Remi (REM) 123

Noble (NBE) 129

Tricia (TCA) 137

Uptown East Village (UPEV) 217

Uptown Theater Row (UPTR) 218

Uptown Madison Manor (UPMM) 222

Uptown Seaport (UPSE) 226

Uptown Holita (UPHL) 226

Millenium (LSM) 318

Yuma (YU) 318

Tiffany - many styles available
See section starting on p. 459

Bath - many styles available
See section starting on p. 321

Bath Lighting

Bram (PCBM) 322

Pierre (PCPR) 323

Endless (PCED) 323

Valiant (PCVT) 324

Blade (PCBD) 324

Pace (PCPC) 325

Promenade (PCPE) 325

Dash (PCDH) 326

Glacial (PCGL) 326

Alexa (PCAX) 327

Shimmer (PCSR) 328

Seaview (PCSW) 329

Serena (PCSA) 330

Lacombe (PCLC) 331

Mirabella (PCMR) 331

Divine (PCDV) 332

Devlin (DVN) 333

Downtown (DW) 334-335

Erin (ERN) 336

Tatum (TU) 337

Quinton (QI) 338

Nolan (NN) 339

Kolt (KLT) 340-341



Adano (AN) 342

Broadgate (BGT) 343

Bower (BWR) 344

Dublin (DBN) 345

Duchess (DH) 346-347

Hollister (HS) 348

Deluxe (DX) 349

Edison (EDS) 350

Garrison (GRN) 351

Demitri (DI) 352-354

Loft (LFT) 355

Melody (MLD) 356

Menlo (MNO) 357

Bath Lighting

Pacifica (PF) 358-359



Nicholas (NL) 360

North Gate (NGT) 361

Parallel (PRL) 362

Supreme (SPR) 363

Tritan (TT) 364

Tranquil Bay (TB) 365

Taylor (TY) 366-367

Paragon (PRN) 368

Evermore (EME) 369

Royale (RYE) 370

Outdoor Lighting

New England (NA) 119

Zephyr (ZP) 240

Monument (MNT) 372

Newbury (NY) 373-379

Alto (ALT) 380

Ryland (RYD) 380

Cole (COE) 381

Stonington (SNN)
382-385

Cathedral (CAT)
386-389

Fort Quinn (FQ) 390-393

Bedford (BFD) 394-395

Tudor (TDR) 396-397

Marblehead (MBH)
398-400

Crestview (CVW) 401

Miles (MLS) 402-403

Booker (BKR) 404-405

Hunter (HTR) 406-407

Oasis (OAS) 408-409

Harmony (HY) 410-411

Hillcrest (HC/HCE)
412-415

Lodge (LDG) 416-417

Millhouse (MHE)
418-419

Rue de Royal (RO)
420-421

Chalmers (CM) 422-423

Cooper (COR) 424-425

Outdoor Lighting

Marine (MRE) 426-427

Devon (DE) 428-429

Ridge (RGE) 430-431

Rutledge (RJ) 432-433

Byron (BRN) 434-435

Steadman (SDN) 436-437

Galen (GLN) 438-440

Chancellor (CCR) 441

Trumbull (TML) 442-443

Province (PRV) 444-445

Powell (PWL) 446-447

Bain (BAN) 448-450

Seaford (SFD) 451

Grover (GVR) 452-453

Georgetown (GT) 454-455

Chimera (CHI) 456-457

Milan (MLN) 458

Victory (TFVY) 460-461

Alcott (TFAT) 462-463

Inglenook (TFIK) 464-468

Carroll 469

Asheville (TFAS) 470-474

Larissa 475

Kami (TFKM) 476-478

Stephen (TFST) 479-481

Monteclaire (TFMC) 482

Belle Fleur (TFBF) 483

West End 484-485

Pomeroy 486

Gotham 486

Hyacinth 487

Pueblo 488, 489

Montgomery 488

Jewel Dragonfly (TFJD) 490

King 491

Copperfly 491

Arden 492

Revere 492



Orange Butterfly 493

Green Frog 493

Flowered Ladybug 493

Lounging Frog 493

Tiffany

Angel Fish 493

Rainbow Butterfly 493

Flower Turtle 493

Purple Wisteria 494

Laburnum 494

Lynch 494

Mariah 495

Jewel 495

Berkshire 495

Alahambre 496

Graham 496

Reed 496

Grove Park 497

Indus 497

Lucia 498

Queens Meadow 498

Connie 498

Adriana 499

Florentine 499

Lance 500

Pearson 500

Ava 501

Chastain 501

Bryant 502

Holmes 502

Bragg Creek 503

Navajo 503

Gibbons 503

Palmetto 504

Fields 504

Cambridge 504

India 505

Viking 505

Jewel Heart 505

Lennon 506

Kelso 506

Classic Craftsman 506

Table&Floor

Kyle (KY) 73

Union Station (UST) 140

Confetti (CKCF) 208

Brookmont (CKBT) 212

Hickman (CKHM) 212

Laguna (MCLG) 229

Alistar(MC) 233

Prism (MC) 233

Cyrus (MCCS) 234

San Gabriel 234

Pearce (PER) 236

Vega (MC) 236

Highland (MC) 237

Tartan (MC) 238

Whispering Wood (AG) 238

Pomez 243

Captiva (SSCV) 244

Floret (SSFT) 244

Sanibel (SSSB) 245

Flower Field (JD) 245

Kingsley (VVKY) 508-509

Benedict (VVBT) 510

Cruise (VVCS) 510

Ambrose (VVAM) 511

Whitney (VVWH) 511

Spencer (VVSP) 512

Thompson (VVTH) 512

Buckler 513

Stockton 514-515

Archer 515

Humphrey 516

Innovation 516

Jensen 516

Haskell 517

Lyndhurst 517

Weaving 517

Jenkins 517

Bray 517

Marx 518

Sway 518

Encore 518

Westway 519

Studio 519

Blaine 519

Ocean 520

Slade 520

Blue River 520

Dune 520

Looping 521

Sable 521

Starling 521

Percy 521

Aquatic 521

Barrel 522

Seaside 522

Abbey 522

Sandy 522

Garnet 523

Satin Lace 523

Abigail Adams 523

Linear 524

Beckett 524

Table&Floor

Glenhaven 524

String Shade 524

Tiffany - many styles available

See section starting on p. 459

Mirror

Woodmere 528

Carrigan 528

Hearst 528

Vanderbilt 528

Finn 529

Sage 529



Tallon 529

Soho 529

Duchess 530

Greystone 530

Jasper 530

Taylor 530

Gwyneth 531

Monterey Mosaic 531

Maxim 531

Shelburne 531

Downtown 532

Norton 532

Ritz 532

Envision 532

Breckenridge 533

Marcos 533

Vista 533

Confetti 533

Ultra 533

At Quoizel, we constantly strive to ensure that the metal and glass finishes shown in the catalog match our actual products. However, variations in printing and chemical finishes may cause some differences between the printed images and actual product.

COLLECTIONS | QUOIZEL

Whether your décor is traditional, contemporary, or somewhere in the middle, Quoizel presents a diverse offering of coordinated lighting tions which will complement and enhance your home.

Browse the pages which follow and find that unique **Quoizel Collection** which fits your own personal style!

From the **DURY COLLECTION** (page 58)
Hanging Fixture: **RDY5208PN**

Adonis COLLECTION

FINISH:
Dark c herry

GLASS:
o pal etched and c lear Water

DAMP **ADS8701DC**

DAMP **ADS5005DC**

ADS639DC DAMP

DAMP ADS1504DC

DAMP ADS1615DC

DAMP ADS2818DC

Adonis COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
ADS1504DC	7.5" H*, 4.5" W, 4.5" Dp.	6"	-	1-100W Med. Base **or** 23W CFL
ADS1615DC	9" H, 15" W, 15" Dp.	-	-	2-60W Med. Base **or** 13W CFL
ADS2818DC	28" H, 18" W, 18" Dp.	6"	-	3-100W Med. Base **or** 23W CFL
ADS5005DC	22" H, 26" W, 26" Dp.	6"	-	5-60W Cand. Base
ADS639DC	19"H**, 39" W, 19.5" Dp.	8" x 4.5"	-	6-60W Cand. Base
ADS8701DC	14" H, 5.5" W, 7" Ext.	5.5" x 5.5"	9.75"	1-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire.
*Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods

Baroness COLLECTION

FINISH:
Western Bronze

SHADE:
Wire

DAMP **BNS1505WT**

NEW!
FOR ◆ 2016

DAMP **BNS5009WT**

BNS5005WT DAMP

DAMP BNS2818WT

NEW!
FOR ◆ 2016

DAMP BNS1715WT



BNS5204WT DAMP

Baroness COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
BNS1505WT	8.5" H*, 5" W, 5" Dp.	1.25" x 5"	1-60W Vintage Bulb Supplied**
BNS1715WT	15.5" H, 15.5" W, 15.5" Dp.	1.5" x 5.5"	3-60W Vintage Bulb Supplied**
BNS2818WT	27.5" H, 18" W, 18" Dp.	5"	4-60W Vintage Bulb Supplied**
BNS5005WT	24" H, 25" W, 25" Dp.	5"	5-60W Vintage Bulb Supplied**
BNS5009WT†	33" H, 33" W, 33" Dp.	5"	9-60W Vintage Bulb Supplied**
BNS5204WT†	31" H, 15" W, 15" Dp.	5"	4-60W Vintage Bulb Supplied**

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. †Fixture comes with 12' of wire and 8' of chain.
*Comes with (2) 12" and (2) 6" Rods. **Max Wattage: 100W Med. Base **or** 23W CFL

Brook Hall COLLECTION

FINISH:
Western Bronze

DAMP **BKH1714WT**

NEW!
FOR ◆ 2016

BKH838WT DAMP

PAINTED BRASS ACCENTS

BKH5208WT DAMP

DAMP BKH5204WT

NEW!
FOR ◆ 2016

DAMP BKH5303WT

Brook Hall COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BKH1714WT	14" H, 14" W, 14" Dp.	6"	3-100W Med. Base **or** 23W CFL
BKH5204WT†	28.5" H, 13" W, 13" Dp.	5"	4-60W Cand. Base
BKH5208WT†	43" H, 18" W, 18" Dp.	5" x 5"	8-60W Cand. Base
BKH5303WT	25" H, 10" W, 10" Dp.	5"	3-60W Cand. Base
BKH838WT	15.5" H, 38" W, 12" Dp.	9" x 4.75"	8-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. †Fixture comes with 12' of wire and 8' of chain.

Buchanan COLLECTION

FINISH:
Western Bronze

GLASS:
clear Seedy

NEW!
FOR ◆ 2016

BCN5009WT DAMP

BCN5006WT DAMP

DAMP BCN2820WT

DAMP BCN5204WT

NEW!
FOR ◆ 2016

DAMP BCN1716WT

Buchanan COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BCN1716WT	14.5" H, 16" W, 16" Dp.	1" x 6"	3-100W Med. Base **or** 23W CFL
BCN2820WT	25.5" H, 20" W, 20" Dp.	.75" x 5"	4-100W Med. Base **or** 23W CFL
BCN5006WT	20" H, 25" W, 25" Dp.	1" x 6"	6-60W Cand. Base
BCN5009WT†	30" H, 33" W, 33" Dp.	1" x 6"	9-60W Cand. Base
BCN5204WT†	26.5" H, 14.5" W, 14.5" Dp.	1" x 6"	4-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. †Fixture comes with 12' of wire and 8' of chain.

Downtown COLLECTION

FINISH:
C Polished c hrome **D** Dusk Bronze NEW!

GLASS:
o pal etched

DW5015D

NEW!
FOR ◆ 2016

Downtown COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DW5015C/D	41.5" H, 44" W, 44" Dp.	6"	15-100W Med. Base **or** 23W CFL

Chain-hung fixture comes with 12' of wire and 8' of chain.

From the **DOWNTOWN COLLECTION:**
DW5005C
Photo courtesy of Innovative Custom Homes

Downtown COLLECTION

FINISH:
C Polished c hrome **D** Dusk Bronze NEW! **BN** Brushed n ickel NEW!

GLASS:
o pal etched

DAMP 50 **DW5009C**

DAMP **DW5005D**

NEW!
FOR ◆ 2016

DW5004C DAMP

Downtown COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DW5004C/D	19.5" H, 22" W, 22" Dp.	6"	4-100W Med. Base **or** 23W CFL
DW5005C/D	26" H, 28" W, 28" Dp.	6"	5-100W Med. Base **or** 23W CFL
DW5009C/D†	33" H, 36" W, 36" Dp.	6"	9-100W Med. Base **or** 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. †Fixture comes with 12' of wire and 8' of chain.

DW43222BN

MOUNTS

NEW!
FOR ◆ 2016

DAMP DW8701BN

DAMP DW8602CLED

DAMP DW8603BNLED

MOUNTS

NEW!
FOR ◆ 2016

DAMP DW8604BNLED

Downtown COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DW43222BN	32" H, 22" W, 1.5" Dp.	-	-	-
DW8602BNLED/CLED	7.5" H, 15" W, 7" Ext.	8" x 5"	5"	2-4.5W Frosted G9 LED Dimmable Bulb Supplied
DW8603BNLED/CLED	7.5" H, 24.5" W, 7" Ext.	8" x 5"	5"	3-4.5W Frosted G9 LED Dimmable Bulb Supplied
DW8604BNLED/CLED	7.5" H, 33.5" W, 7" Ext.	8" x 5"	5"	4-4.5W Frosted G9 LED Dimmable Bulb Supplied
DW8701BN/C	10.5" H, 6" W, 8" Ext.	8" x 5"	7.75"	1-100W Med. Base **or** 23W CFL

Downtown bath fixtures can be mounted as uplights or downlights. DW43222BN can be mounted vertically or horizontally.

From the **DOWNTOWN COLLECTION:**
DW2817C
Photo courtesy of Phil Kean Design Group

Downtown COLLECTION

FINISH:
C Polished c hrome **D** Dusk Bronze NEW!

GLASS:
o pal etched

DW1506D

NEW!
FOR ◆ 2016

DW1824D



DW2817C

DW1717C

Downtown COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.	SHADE
DW1506C/D	12.5" H*, 6" W, 6" Dp.	5.5"	1-100W Med. Base **or** 23W CFL	-	
DW1717C/D	13.5" H, 17" W, 17" Dp.	8"	3-100W Med. Base **or** 23W CFL	17" x 5.5"	Cream Linen
DW1824C/D	33" H, 24" W, 24" Dp.	6"	4-100W Med. Base **or** 23W CFL	24" x 8"	Cream Linen
DW2817C/D	24" H, 17" W, 17" Dp.	6"	3-75W Med. Base **or** 18W CFL	17" x 7.5"	Cream Linen

Chain-hung fixtures come with 8' of wire and 4' of chain.
*Comes with (2) 6" and (2) 12" Rods. Rod-hung fixtures come with 8' of wire.

Duchess COLLECTION

FINISH:
AN Antique Nickel
PN Palladian Bronze

GLASS:
AN Grey Marble
PN Champagne Marble

DH5009AN DAMP

DH5018AN

DH5105PN

DH5005PN

DuchessCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH5005AN/PN*	22.5" H, 24.5" W, 24.5" Dp.	6.5"	5-100W Med. Base **or** 23W CFL
DH5009AN/PN**	31" H, 31" W, 31" Dp.	6.5"	9-100W Med. Base **or** 23W CFL
DH5018AN/PN**	39" W, 41" H, 41" Dp.	6.5"	18-100W Med. Base **or** 23W CFL
DH5105AN/PN*	21" H, 24.5" W, 24.5" Dp.	6.5"	5-100W Med. Base **or** 23W CFL

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.

Duchess COLLECTION

FINISH:
AN Antique n ickel
PN Palladian Bronze

GLASS:
AN Grey Marble
PN c hampagne Marble

DAMP **DH5103AN**

DH2820AN DAMP

DAMP **DH348PN**

Duchess COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH2820AN/PN	24" H, 20" W, 20" Dp.	6.5"	4-100W Med. Base **or** 23W CFL
DH348AN/PN	27" H, 48" W, 14" Dp.	6.5"	3-100W Med. Base **or** 23W CFL
DH5103AN/PN	20" H, 23" W, 23" Dp.	6"	3-100W Med. Base **or** 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

From the **DUCHESS COLLECTION:**
DH2820PN

Duchess COLLECTION

FINISH:
AN Antique n ickel
PN Palladian Bronze

GLASS:
AN Grey Marble
PN c hampagne Marble

DAMP **DH1718PN**

DAMP **DH1506PN**

Enlarged for detail

DAMP **DH1404AN**

All Quoizel Track Lights Swivel

DH8601AN DAMP

DH8602PN DAMP

MOUNTS

DAMP DH8603AN

DH44030PN

MOUNTS

DH8604PN DAMP

Duchess COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
DH1404AN/PN	12.5" H, 36.5" W, 6" Dp.	4.5"	-	4-100W Med. Base **or** 23W CFL	-
DH1506AN/PN	11" H*, 6" W, 6" Dp.	5.5"	-	1-100W Med. Base **or** 23W CFL	-
DH1718AN/PN	11" H, 17" W, 17" Dp.	5.5"	-	3-100W Med. Base **or** 23W CFL	-
DH43024PN**	30" H, 24" W, 1.5" Dp.	-	-	-	Beveled
DH44030PN	40" H, 30" W, 1.5" Dp.	-	-	-	Beveled
DH8601AN/PN	11" H, 6" W, 8" Ext.	4.75" x 6.75"	7.5"	1-100W Med. Base **or** 23W CFL	-
DH8602AN/PN	11" H, 16" W, 7.5" Ext.	9" x 5"	7.5"	2-100W Med. Base **or** 23W CFL	-
DH8603AN/PN	11" H, 23" W, 7.5" Ext.	9" x 5"	7.5"	3-100W Med. Base **or** 23W CFL	-
DH8604AN/PN	11" H, 31.5" W, 7.5" Ext.	9 x 5	7.5"	4-100W Med. Base **or** 23W CFL	-

**Not Shown. *Comes with (2) 6" and (2) 12" Rods. Duchess bath fixtures can be mounted as uplights or downlights.
All rod-hung fixtures come with 8' of wire. Mirrors may be hung vertically or horizontally.

Dury COLLECTION

FINISH:

CS century Silver leaf

PN Palladian Bronze

RDY5208CS

Dury COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RDY5208CS/PN**	36" H, 24.5" W, 24.5" Dp.	1" x 5.5"	8-60W Cand. Base

Chain-hung fixture comes with 12' of wire and 8' of chain.

From the **DURY COLLECTION:**
RDY1714CS

Dury COLLECTION

FINISH:

CS century Silver leaf

PN Palladian Bronze

VINTAGE STYLE
bulb included



DAMP **RDY1506CS**

DAMP **RDY2823PN**

RDY1714PN DAMP

FAUX MELTED WAX CANDLES

DAMP **RDY2821CS**

Dury COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RDY1506CS*	11" H, 6.5" W, 6.5" Dp.	5"	1-60W Vintage Bulb (Supplied)†
RDY1714CS/PN	14.5" H, 14.5" W, 14.5" Dp.	.75" x 5.5"	3-60W Cand. Base
RDY2821CS/PN	15" H, 21" W, 21" Dp.	5"	4-60W Cand. Base
RDY2823CS/PN	20" H, 23" W, 23" Dp.	1" x 5.5"	4-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. †Max wattage: 100W Med. Base **or** 23W CFL.

EmeryCOLLECTION

FINISH:

BN Brushed n ickel **IS** imperial Silver **PN** Palladian Bronze

SHADE: Metal

Available in Three Finishes!

ER5103IS

ER5103PN

DAMP **ER5103BN**

EmeryCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ER5103BN/IS/PN	15" H*, 24" W, 24" Dp.	5"	3-100W Med. Base **or** 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Emery COLLECTION

FINISH:

BN Brushed n ickel

IS imperial Silver

PN Palladian Bronze

SHADE: Metal

ER353PN

ER1508IS

Pendant converts to Semi-Flush Mount

(all finishes)

ER1814BN

Emery COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ER1508BN/IS/PN	9" H*, 8" W, 8" Dp.	5"	1-100W Med. Base **or** 23W CFL
ER1814BN/IS/PN	11.5" H*, 13.5" W, 13.5" Dp.	5"	1-100W Med. Base **or** 23W CFL
ER353BN/IS/PN	23.5" H**, 52.5" W, 13" Dp.	9" x 4.5"	3-100W Med. Base **or** 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods.

From the **EMERY COLLECTION:**
ER1814IS
Photo courtesy of Letitia Little Interior Design

Kendra COLLECTION

FINISH:
Mottled Silver

SHADE:
o yster Mica

ELONGATED CRYSTAL DROPS

KD5015MM

QUOIZEL
NATURALS
MICA

KD5009MM DAMP

QUOIZEL
NATURALS
MICA

DAMP KD5005MM

KD8701MM DAMP

KendraCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
KD5005MM*	31" H, 27" W, 27" Dp.	5.5"	-	5-60W Cand. Base
KD5009MM**	39" H, 34" W, 34" Dp.	5.5"	-	9-60W Cand. Base
KD5015MM**	53" H, 44" W, 44" Dp.	5.5"	-	15-60W Cand. Base
KD8701MM	13.5" H, 6" W, 10" Dp.	4.5" x 6.5"	6.25"	1-60W Cand. Base

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.
Due to natural properties, shade color may vary.

From the **KENDRA COLLECTION:**
KD5009MM

KendraCOLLECTION

FINISH:
Mottled Silver

SHADE:
o yster Mica

QUOIZEL
NATURALS
MICA

KD2824MM

KD1507MM

KD1716MM

KD2816MM

KendraCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
KD1507MM	12" H*, 7" W, 7" Dp.	5.5"	1-100W Med. Base **or** 23W CFL
KD1716MM	12.5" H, 16" W, 16" Dp.	5.5"	3-60W Med. Base **or** 13W CFL
KD2816MM	22" H, 17" W, 17" Dp.	5.5"	2-100W Med. Base **or** 23W CFL
KD2824MM	29" H, 24" W, 24" Dp.	5.5"	4-60W Med. Base **or** 13W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.
Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
Due to natural properties, shade color may vary.

Kyle COLLECTION

FINISH:
IB imperial Bronze
IN iron Gate

SHADE:
IB Butterscotch o nyx
IN White o nyx

QUOIZEL
NATURALS
ONYX

KY5016IB

Kyle COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
KY5016IB	48" H, 42" W, 42" Dp.	7"	16-100W Med. Base **or** 23W CFL

Chain-hung fixture comes with 12' of wire and 8' of chain.

From the **KYLE COLLECTION:**
Hanging Fixture: **KY2822IB** Mini Pendant: **KY1507IB**
Photo courtesy of Devane Design

Kyle COLLECTION

FINISH:
IB imperial Bronze
IN iron Gate

SHADE:
IB Butterscotch o nyx
IN White o nyx

KY5009IN

KY5106IB

KY5006IN

QUOIZEL
NATURALS
ONYX

KY5103IN

Enlarged for detail

Quoizel artisans take the natural beauty of onyx and create unique solutions for home lighting.

KY433IB



KY540IN

QUOIZEL
NATURALS
ONYX

KyleCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
KY433IB*	18.5" H, 33" W, 4.5" Dp.	8" x 4.5"	4-100W Med. Base **or** 23W CFL
KY5006IB/IN*	28" H, 28" W, 28" Dp.	5.5"	6-100W Med. Base **or** 23W CFL
KY5009IB/IN**	34.5" H, 35" W, 35" Dp.	5.5"	9-100W Med. Base **or** 23W CFL
KY5103IB/IN*	22" H, 20" W, 20" Dp.	5.5"	3-100W Med. Base **or** 23W CFL
KY5106IB*	24" H, 24" W, 24" Dp.	1.25" x 5.5"	6-100W Med. Base **or** 23W CFL
KY540IB/IN*	23" H, 40" W, 5.5" Dp.	11.75" x 4.75"	5-100W Med. Base **or** 23W CFL

*Chain-hung fixtures come with 8' of wire and 4' of chain.

**Chain-hung fixture comes with 12' of wire and 8' of chain. Due to natural properties, shade color may vary.

Kyle COLLECTION

FINISH:
IB imperial Bronze
IN iron Gate

SHADE:
IB Butterscotch o nyx
IN White o nyx

DAMP **KY5506IB**

DAMP **KY5503IB**

DAMP **KY2822IB**

QUOIZEL
NATURALS
ONYX

KY1716IB DAMP

KY1404IB DAMP

All Quoizel Track Lights Swivel

KY8801IN DAMP

Enlarged for detail

DAMP KY1507IB

DAMP KY1508IN

QUOIZEL
NATURALS ONYX

KY6328IB

DAMP KY8701IN

KyleCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
KY1404IB	14.5" H, 36" W, 4.5" Dp.	8.25" x 4.5"	-	4-100W Med. Base **or** 23W CFL
KY1507IB/IN	20" H*, 8" W, 8" Dp.	5"	-	1-100W Med. Base **or** 23W CFL
KY1508IB/IN	7" H*, 5" W, 5" Dp.	5"	-	1-100W Med. Base **or** 23W CFL
KY1716IB	11" H, 16" W, 16" Dp.	5"	-	3-100W Med. Base **or** 23W CFL
KY2822IB	22.5" H, 24" W, 24" Dp.	5.5"	-	5-75W Med. Base **or** 18W CFL
KY5503IB	19.5" H, 17" W, 17" Dp.	5.5"	-	3-100W Med. Base **or** 23W CFL
KY5506IB	23" H, 23" W, 23" Dp.	5.5"	-	6-100W Med. Base **or** 23W CFL
KY6328IB	30" H, 14" W, 14" Dp.	-	-	2-100W Med. Base **or** 23W CFL
KY8701IB/IN	16" H, 4.5" W, 5.5" Ext.	4.5" x 8.25"	-	1-100W Med. Base **or** 23W CFL
KY8801IB/IN	11" H, 8.5" W, 4.5" Ext.	4.75" x 4.75"	5.5"	1-75W Med. Base **or** 18W CFL + 1-7W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Comes with (2) 6" and (2) 12" Rods.
Rod-hung fixtures come with 8' of wire. Due to natural properties, shade color may vary.

La Parra COLLECTION

FINISH:
imperial Bronze

GLASS:
Candella Scavo

LP5018IB

LP5009IB DAMP 50

CANDELA SCAVO GLASS

DAMP LP5006IB

La Parra COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
LP5006IB*	30" H, 28" W, 28" Dp.	9"	6-100W Med. Base **or** 23W CFL
LP5009IB**	37" H, 30" W, 30" Dp.	9"	9-100W Med. Base **or** 23W CFL
LP5018IB**	56" H, 47.5" W, 47.5" Dp.	9"	18-100W Med. Base **or** 23W CFL

*Chain-hung fixture comes with 8' of wire and 4' of chain.
**Chain-hung fixtures come with 12' of wire and 8' of chain.

La Parra COLLECTION

FINISH:
imperial Bronze

GLASS:
Candella Scavo

LP639IB

LP8601IB

Enlarged for detail

LP1505IB

La Parra COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
LP1505IB	14.5" H, 5" W, 5" Dp.	5.25"	-	1-100W Med. Base **or** 23W CFL
LP639IB	46" H, 38" W, 19" Dp.	7" x 4.5"	-	6-100W Med. Base **or** 23W CFL
LP8601IB	9" H, 5" W, 7" Ext.	5" x 8"	4.8"	1-100W Med. Base **or** 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

From the **MARQUETTE COLLECTION:**
MQ5003HL
Photo courtesy of Designs on Madison

Marquette COLLECTION

FINISH:
Heirloom

MQ5020HL

MQ5009HL DAMP

MQ8701HL DAMP

DAMP MQ5006HL

Marquette COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MQ5006HL*	38" H, 28" W, 28" Dp.	7"	-	6-60W Cand. Base
MQ5009HL**	41" H, 32" W, 32" Dp.	7"	-	9-60W Cand. Base
MQ5020HL**	60" H, 50" W, 50" Dp.	9"	-	20-60W Cand. Base
MQ8701HL	21.5" H, 8.5" W, 7.5" Dp.	6" x 6"	13.75"	1-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain.
**Chain-hung fixtures come with 12' of wire and 8' of chain.

Marquette COLLECTION

FINISH:
Heirloom

MQ5208HL

MQ5206HL

MQ5003HL

Marquette COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MQ5003HL*	24" H, 17" W, 17" Dp.	7"	3-60W Cand. Base
MQ5206HL**	41.5" H, 20.5" W, 20.5" Dp.	7"	6-60W Cand. Base
MQ5208HL**	55" H, 27" W, 27" Dp.	7"	8-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.

MontereyMosaic COLLECTION

FINISH:
Malaga

SHADE:
Pen Shell Mosaic

QUOIZEL
NATURALS
PEN SHELL

MY5005ML DAMP

MontereyMosaic COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MY5005ML	28.5" H, 25" W, 25" Dp.	5"	5-100W Med. Base **or** 23W

Chain-hung fixture comes with 8' of wire and 4' of chain. Due to natural properties, shade color may vary.

QUOIZEL

NATURALS

PEN SHELL

Quoizel artisans take the natural beauty of pen shell and bring the wonder of the ocean to your home décor.

From the **MONTEREY MOSAIC COLLECTION:**

Mirror: **MY430241ML** Wall Sconce: **MY8801ML** Dinette Fixture: **MY5103ML**

The Monterey Mosaic Collection is made with Pen Shell and is perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.

MontereyMosaic COLLECTION

FINISH:
Malaga

SHADE:
Pen Shell Mosaic

DAMP **MY5103ML**

MY2824ML DAMP

DAMP **MY2816ML**

QUOIZEL
NATURALS
PEN SHELL

MY1618ML DAMP

MY1613ML DAMP

QUOIZEL
NATURALS
PEN SHELL

MY1723ML DAMP

DAMP MY1718ML



MY1404ML DAMP

All Quoizel Track Lights Swivel

MontereyMosaic COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MY1404ML	16.5" H, 43.5" W, 5" Dp.	7.25"	4-100W Med. Base **or** 23W CFL
MY1613ML	7" H, 16" W, 16" Dp.	11"	3-60W Med. Base **or** 13W CFL
MY1618ML	7" H, 18" W, 18" Dp.	.75" x 12"	4-60W Med. Base **or** 13W CFL
MY1718ML	13" H, 18" W, 18" Dp.	2" x 6"	4-100W Med. Base **or** 23W CFL
MY1723ML	14" H, 24" W, 24" Dp.	2" x 6"	5-100W Med. Base **or** 23W CFL
MY2816ML	22" H, 18" W, 18" Dp.	5"	3-100W Med. Base **or** 23W CFL
MY2824ML	28" H, 23.5" W, 23.5" Dp.	5"	4-100W Med. Base **or** 23W CFL
MY5103ML	24" H, 24" W, 24" Dp.	5"	3-100W Med. Base **or** 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.
Due to natural properties, shade color may vary.

MontereyMosaic COLLECTION

FINISH:
Malaga

SHADE:
Pen Shell Mosaic

DAMP **MY1506ML**

MY430241ML

QUOIZEL
NATURALS
PEN SHELL

MY430242ML

DAMP **MY8801ML**

Enlarged for detail

MontereyMosaic COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MY1506ML	18" H*, 6" W, 6" Dp.	5"	-	1-100W Med. Base **or** 23W CFL
MY430241ML	30" H, 24" W, 1.5" Dp.	-	-	-
MY430242ML	30" H, 24" W, 1.5" Dp	-	-	-
MY8801ML	12" H, 9" W, 5" Ext	7" x 4.5"	4.75	2-60W Cand. Base

*Comes with (2) 6" and (2) 12" Rods. Due to natural properties, shade color may vary.

TaylorCOLLECTION

FINISH:
Antique Nickel

GLASS:
Opal Etched

DAMP **TY8501AN**

DAMP **TY5005AN**

TaylorCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TY5005AN	20" H*, 25" W, 25" Dp.	5.5" x .875"	-	5-100W Med. Base **or** 23W CFL
TY8501AN	19.5" H, 5.5" W, 5" Ext..	5.5" x .875"	10"	1-100W Med. Base **or** 23W CFL

*Comes with (2) 12" and (2) 6" Rods. Rod-hung fixtures come with 8' of wire.

From the **TAYLOR COLLECTION**
Mirror: **TY43625AN** Wall Fixture: **TY8501AN** Chandelier: **TY5005AN**

Taylor COLLECTION

FINISH:
AN Antique n ickel
BN Brushed n ickel NEW!
WT Western Bronze
C Polished Chrome

GLASS: o pal etched

DAMP **TY628AN**

DAMP **TY1721AN**

TY1716AN DAMP

TY1444WT DAMP

NEW!
FOR ◆ 2016

All Quoizel Track Lights Swivel

DAMP **TY1404AN**

TY43625AN

DAMP TY8601C

Enlarged for detail

TY8602C DAMP

DAMP TY8603C

MOUNTS

Taylor bath fixtures are also available in Antique Nickel, Brushed Nickel and Western Bronze finishes.

NEW! FOR ◆ 2016

DAMP TY8604C

TaylorCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
TY1404AN	8.5" H, 43" W, 3" Dp.	.875" x 9"	-	4-60W Frosted G9 Halogen†	-
TY1444AN/WT	11" H, 44" W, 5" Dp.	9" x 4.75"	-	4-100W Med. Base **or** 23W CFL	-
TY1716AN	11.5" H, 16.5" W, 16.5" Dp.	5.5" x .875"	-	3-100W Med. Base **or** 23W CFL	Etched Painted White Inside
TY1721AN	13.5" H, 21" W, 21" Dp.	5.5" x .875"	-	4-100W Med. Base **or** 23W CFL	Etched Painted White Inside
TY43625AN	35.5" H, 25.5" W, 2" Dp.	-	-	-	Beveled
TY628AN	16.5" H*, 28" W, 16" Dp.	.875" x 9"	-	6-100W Med. Base **or** 23W CFL	-
TY8601AN/BN/C	7.5" H, 4.5" W, 5.5" Ext.	4.5" x 5"	5"	1-100W Med. Base **or** 23W CFL	-
TY8602AN/BN/C/WT	7.5" H, 13.5" W, 5.5" Ext.	7" x 4.5"	5.5"	2-100W Med. Base **or** 23W CFL	-
TY8603AN/BN/C/WT	7.5" H, 21" W, 5.5" Ext.	7" x 4.5"	5.5"	3-100W Med. Base **or** 23W CFL	-
TY8604AN/BN/C/WT	7.5" H, 30" W, 5.5" Ext.	7" x 4.5"	5.5"	4-100W Med. Base **or** 23W CFL	-

Rod-hung fixtures come with 8' of wire. *Comes with (4) 6" and (4) 12" Rods. †Bulbs Supplied.
Taylor bath fixtures may be mounted as uplights or downlights.

From the **TRILOGY COLLECTION:**
TRG5103OZ

Trilogy COLLECTION

FINISH:
o ld Bronze

SHADE:
Clear Seedy

TRG5105OZ DAMP

Trilogy COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
TRG5105OZ	19" H, 26.5" W, 26.5" Dp.	5"	5-60W Vintage Bulb Supplied*

*Max Wattage: 100W Med. Base **or** 23W CFL

Trilogy COLLECTION

FINISH:
o ld Bronze

GLASS:
Clear Seedy

DAMP **TRG5103OZ**

DAMP **TRG1816OZ**



DAMP **TRG1508OZ**

TRG1712OZ DAMP

DAMP TRG1716OZ

CLEAR SEEDY GLASS

TRG8701OZ DAMP



Trilogy COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TRG15080Z	7.5" H*, 8" W, 8" Dp.	5"	-	1-60W Vintage Bulb Supplied**
TRG17120Z	10" H, 12" W, 12" Dp.	5"	-	1-60W Vintage Bulb Supplied**
TRG17160Z	12" H, 16" W, 16" Dp.	5"	-	3-60W Vintage Bulb Supplied**
TRG18160Z	20" H, 16" W, 16" Dp.	5"	-	3-60W Vintage Bulb Supplied**
TRG51030Z	17.5" H, 22" W, 22" Dp.	5"	-	3-60W Vintage Bulb Supplied**
TRG87010Z	9.5" H, 8" W, 9" Ext	5" x 5"	3"	1-60W Vintage Bulb Supplied**

Chain-hung fixtures come with 8' of wire and 4' of chain.
*Comes with (2) 6" and (2) 12" Rods. All rod-hung fixtures come with 8' of wire.
Max Wattage: 100W Med. Base **or 23W CFL

Whitney COLLECTION

FINISH:
imperial Silver

SHADE:
White o rganza with Dark Grey t rim

WHI5012IS

WHI5009IS DAMP

CRYSTAL DROPS

DAMP WHI8701IS

Enlarged for detail

Whitney COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
WHI5009IS**	33" H, 32" W, 32" Dp.	6"	-	9-60W Cand. Base	5" x 4.5" x 5"
WHI5012IS**	38" H, 39" W, 39" Dp.	6"	-	12-60W Cand. Base	5" x 4.5" x 5"
WHI8701IS	16" H, 7" W, 7" Dp.	4.5" x 7"	12"	1-60W Cand. Base	5" x 4.5" x 5"

**Chain-hung fixtures come with 12' of wire and 8' of chain.

From the **WHITNEY COLLECTION**
Hanging Fixture: **WHI5005IS** Wall Fixture: **WHI8701IS**

Whitney COLLECTION

FINISH:
imperial Silver

SHADE:
White o rganza with Dark Grey t rim

DAMP **WHI5005IS**

WHI1716IS DAMP

Whitney COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
WHI1716IS	16.5" H, 16" W, 16" Dp.	6"	-	3-60W Cand. Base	6" x 14.5" x 16"
WHI5005IS	27" H, 28" W, 28" Dp.	6.5"	-	5-60W Cand. Base	5" x 4.5" x 5"

Chain-hung fixtures come with 8' of wire and 4' of chain.

From the **GRANT COLLECTION: GRT1508BN** (p. 115)

Photo courtesy of Dovetail Group LLC and Terry Scholl Photography

Adams COLLECTION

FINISH:
Leathered Bronze

SHADE:
White Linen Hardback

NEW!
FOR ◆ 2016

ADA5009LN DAMP

ADA5006LN DAMP

ADA2820LN DAMP

ADA8702LN DAMP

Enlarged for detail

NEW!
FOR ◆ 2016

Adams COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
ADA2820LN	23" H*, 18.5" W, 18.5" Dp.	5"	-	4-100W Med. Base **or** 23W CFL	6" x 17" x 17"
ADA5006LN	10.5" H*, 25" W, 25" Dp.	5"	-	6-60W Cand. Base	5" x 5.5" x 5.5"
ADA5009LN	19.5" H**, 29.5" W, 29.5" Dp.	5"	-	9-60W Cand. Base	5" x 5.5" x 5.5"
ADA8702LN	13.5" H8, 12" W, 6" Ext.	5" x 5"	2.75"	2-60W Cand. Base	6" x 11.75" x 11.75"

*Rod-hung fixtures come with 10' of wire. **Rod-hung fixture comes with 12' of wire.
All rod hung fixtures come with 2 (6)" and (2) 12" Rods.

Alexandria COLLECTION

FINISH:
Palladian Bronze

AX2826PN DAMP

AX2820PN DAMP

AX434PN DAMP

DANGLING GLASS ACCENTS



Alexandria COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
AX2820PN	8" H*, 19.5" W, 19.5" Dp.	.75" x 5"	5-100W Med. Base **or** 23W CFL
AX2826PN	14" H*, 26" W, 26" Dp.	.75" x 5"	6-100W Med. Base **or** 23W CFL
AX434PN	8" H**, 33.5" W, 15.5" Dp.	4.5"	4-100W Med. Base **or** 23W CFL

All rod-hung fixtures come with 10' of wire. *Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods.

Eastvale COLLECTION

FINISH:
Palladian Bronze

SHADE:
Metal

Pendant converts to Semi-Flush Mount

EVE240PN



EVE2815PN



RIBBED GLASS DIFFUSER

EVE1508PN

EVE1404PN

All Quoizel Track Lights Swivel

Eastvale COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
EVE1404PN	10.5" H, 36.5" W, 3.5" Dp.	5"	4-50W MR-16 with GU10 Shielded Bulb Supplied
EVE1508PN*	9.5" H**, 8" W, 8" Dp.	6"	1-100W Med. Base **or** 23W CFL
EVE240PN*	29" H**, 40" W, 14.5" Dp.	6"	2-100W Med. Base **or** 23W CFL
EVE2815PN*	12" H**, 14.5" W, 14.5" Dp.	6"	1-100W Med. Base **or** 23W CFL

*Rod-hung fixtures come with 8' of wire. **Comes with (2) 6" and (2) 12" Rods.

Chamber COLLECTION

FINISH:
Darkest Bronze

CHB5208DK



CHB5206DK

QUOIZEL
NATURALS
WOOD

CHB5204DK

CHB1612DK





Chamber COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
CHB1612DK	16" H, 12" W, 12" Dp.	5.5"	1-60W Vintage Bulb Supplied
CHB5204DK	21" H, 16" W, 16" Dp.	5.5"	4-60W Cand. Base
CHB5206DK	29" H, 24" W, 24" Dp.	5.5"	6-60W Cand. Base
CHB5208DK	35.5" H, 30.5" W, 30.5" Dp.	5.5"	8-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain. *Max Wattage: 1-100W Med. Base **or** 23W CFL.

From the **CHAMBER COLLECTION: CHB5204DK**

Armelle COLLECTION

FINISH:
Imperial Bronze

SHADE:
Butterscotch o nyx

AME5018IB

QUOIZEL
NATURALS
ONYX

QUOIZEL
NATURALS ONYX

AME5009IB DAMP

DAMP AME8701IB

Enlarged for detail

AME5005IB DAMP

Armelle COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
AME5005IB	23" H, 28" W, 28" Dp.	5"	-	5-60W Cand. Base
AME5009IB*	33" H, 33" W, 33" Dp.	5"	-	9-60W Cand. Base
AME5018IB*	48" H, 48" W, 48" Dp.	6"	-	18-60W Cand. Base
AME8701IB	9.5" H, 5" W, 6.5" Ext	4.63" x 7"	4"	1-60W Cand. Base

Chain-hung fixture comes with 8' of wire and 4' of chain. *Fixtures come with 12' of wire and 8' of chain.

Baron COLLECTION

FINISH:
Marcado Black

QUOIZEL
NATURALS
WOOD

DAMP **BRO5203MK**

BRO5204MK DAMP

BRO1715MK DAMP

Baron COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BRO1715MK	14.5" H, 15" W, 15" Dp.	5"	3-60W Cand. Base
BRO5203MK	27.5" H, 15.5" W, 15.5" Dp.	5"	3-60W Cand. Base
BRO5204MK	39" H, 18" W, 18" Dp.	5"	6-60W Cand. Base

All chain-hung fixtures come with 12' of wire and 8' of chain.

Castile COLLECTION

FINISH:
Rustic Black

QUOIZEL
NATURALS
WOOD

DAMP **CS5012RK**

DAMP **CS1718RK**

DAMP **CS5006RK**

Castile COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
CS1718RK	15.5" H, 18" W, 18" Dp.	5" x 0.75"	4-60W Cand. Base
CS5006RK*	22.5" H, 29" W, 29" Dp.	5" x 0.75"	6-60W Cand. Base
CS5012RK**	27" H, 35.5" W, 35.5" Dp.	6.5" x 1.25"	12-60W Cand. Base

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.

From the **MILBANK COLLECTION:**
MBK5005VG

Milbank COLLECTION

FINISH:
Vintage Gold

GLASS:
o pal etched

DAMP **MBK5005VG**

MBK2820VG DAMP

DAMP **MBK1716VG**

Milbank COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MBK1716VG	11" H, 16" W, 16" Dp.	5.5"	3-100W Med. Base **or** 23W CFL
MBK2820VG	26" H, 20.5" W, 20.5" Dp.	5.5"	4-100W Med. Base **or** 23W CFL
MBK5005VG	26.5" H, 25" W, 25" Dp.	5.25"	5-100W Med. Base **or** 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

Grant COLLECTION

FINISH:

BN Brushed Nickel

IS Imperial Silver

PN Palladian Bronze

GLASS: o pal etched

DAMP **GRT5103BN**

Available in Three Finishes!

GRT5103IS

GRT5103PN

GRT2814BN

Pendant converts to Semi-Flush Mount

(all finishes)

GRT2814PN

GRT1508BN

GRT1508IS

Grant COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
GRT1508BN/IS/PN	9.5" H*, 8" W, 8" Dp.	5"	1-100W Med. Base **or** 23W CFL
GRT2814BN/IS/PN	11.5" H*, 13.5" W, 13.5" Dp.	5"	1-100W Med. Base **or** 23W CFL
GRT5103BN/IS/PN	15.5" H*, 24" W, 24" Dp.	5"	3-100W Med. Base **or** 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with 2 (6)" and (2) 12" Rods.

Laila COLLECTION

FINISH:
Rustic Antique Bronze

LLA5205RA

LLA5204RA

LLA5203RA

LLA1615RA

Laila COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
LLA1615RA	14.5" H, 15" W, 15" Dp.	8"	3-60W Cand. Base
LLA5203RA*	20" H, 15" W, 15" Dp.	5.5"	3-60W Cand. Base
LLA5204RA**	21" H, 18" W, 18" Dp.	5"	4-60W Cand. Base
LLA5205RA**	26.5" H, 22" W, 22" Dp.	5.5"	5-60W Cand. Base

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.

Metropolis COLLECTION

FINISH: Antique Nickel
SHADE: Metal with Inner o pal etched Glass

NEW!
FOR ◆ 2016

MTP2823AN DAMP



Pendant converts to Semi-Flush Mount

MTP5203AN DAMP

Enlarged for detail

MTP1510AN DAMP

MTP2820AN DAMP

Pendant converts to Semi-Flush Mount

MTP1718AN DAMP

Metropolis COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MTP1510AN	12" H, 10" W, 10" Dp.	5"	1-100W Med. Base **or** 23W CFL
MTP1718AN	9" H, 18" W, 18" Dp.	.75" x 7.75"	3-75W Med. Base **or** 18W CFL
MTP2820AN	9" H, 20" W, 20" Dp.	4.75"	3-100W Med. Base **or** 23W CFL
MTP2823AN	9" H, 23" W, 23" Dp.	4.75"	4-100W Med. Base **or** 23W CFL
MTP5203AN*	20" H, 16" W, 16" Dp.	4.75"	3-100W Med. Base **or** 23W CFL

Rod-hung fixtures come with 8" of wire. Comes with (2) 6" and (2) 12" Rods. **Comes with 12" of wire.

NewEnglandCOLLECTION

FINISH:
BN Brushed Nickel
PN Palladian Bronze

GLASS:
Acid etched

NA5103BN DAMP

NA1510BN DAMP

NA1514BN DAMP

NA8414PN WET

WET NA8409PN

INDOOR OUTDOOR

NewEnglandCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
NA1510BN	11" H*, 9.5" W, 9.5" Dp.	5.25"	-	1-100W Med. Base **or** 23W CFL
NA1514BN	9.5" H*, 14" W, 14" Dp.	5.25"	-	1-100W Med. Base **or** 23W CFL
NA5103BN	22.5" H, 25" W, 25" Dp.	5"	-	3-100W Med. Base **or** 23W CFL
NA8409PN	9.5" H, 9.5" W, 10" Dp.	5.25" x 5.25"	4.5"	1-100W Med. Base **or** 23W CFL
NA8414PN	11.5" H, 14.5" W, 15.5" Dp.	7" x 7"	5.5"	1-100W Med. Base **or** 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire.
*Comes with (2) 6" and (2) 12" Rods.

Tavern COLLECTION

FINISH:
Darkest Bronze

DAMP **TVN5005DK**



QUOIZEL
NATURALS
WOOD

DAMP **TVN232DK**

DAMP **TVN1717DK**

Tavern COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
TVN1717DK	14.5" H, 17" W, 17" Dp.	5.5"	3-60W Vintage Bulbs Supplied†
TVN232DK	10.5" H*, 32" W, 12" Dp.	10.5" x 4.5"	6-60W Vintage Bulbs Supplied†
TVN5005DK	13" H**, 26" W, 26" Dp.	6"	5-60W Vintage Bulbs Supplied†

Rod-hung fixtures come with 8' of wire. *Comes with (4) 6" and (4) 12" Rods. **Comes with (2) 6" and (2) 12" Rods.
†Max Wattage: 100W Med. Base **or** 23W CFL.

From the **TAVERN COLLECTION: TVN232DK**

Palmer COLLECTION

FINISH:
Palladian Bronze

SHADE:
o uter: l ight Amber o rganza with Brown t rim
Inner: etched Glass

PLR5005PN DAMP

PLR2820PN DAMP

DAMP **PLR1716PN**

Palmer COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
PLR1716PN	14.5" H, 16" W, 16" Dp.	4.75"	3-100W Med. Base **or** 23W CFL
PLR2820PN	23.5" H, 20" W, 20" Dp.	5"	3-100W Med. Base **or** 23W CFL
PLR5005PN	21" H, 25" W, 25" Dp.	5"	5-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

RemiCOLLECTION

FINISH:
Polished Chrome

SHADE:
White Fabric

REM345C DAMP

REM5004C DAMP

REM8701C DAMP

Enlarged for detail

RemiCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
REM345C	10" H, 44.5" W, 5.5" Dp.	4.5" Sq.	-	3-75W Med. Base **or** 18W CFL	6" x 10.5" x 5.5"
REM5004C	13.5" H*, 29" W, 29" Dp.	4.5" Sq.	-	4-75W Med. Base **or** 18W CFL	6" x 10.5" x 5.5"
REM8701C	11" H, 10.5" W, 6.5" Dp.	4.5" Sq.	8.5"	1-60W Med. Base **or** 13W CFL	6" x 10.5" x 5.5"

Cable-hung fixture comes with 12' of wire. Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

Odell COLLECTION

FINISH:
Imperial Bronze

SHADE:
Metal Mesh

QUOIZEL
NATURALS
WOOD

NEW!
FOR ◆ 2016

ODL5009IB DAMP

ODL5005IB DAMP

NEW! FOR ◆ 2016

DAMP ODL5206IB

QUOIZEL NATURALS WOOD

ODL2820IB DAMP

Pendant converts to Semi-Flush Mount

ODL5303IB DAMP

Metal Mesh is quickly becoming a popular material in home lighting, for a dramatic and contemporary diffused look.

Odell COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ODL2820IB	30" H, 20" W, 20" Dp.	1.25" x 6"	5-60W Cand. Base
ODL5005IB	29.5" H, 28.5" W, 28.5" Dp.	1.5" x 6"	5-60W Cand. Base
ODL5009IB*	39" H, 33.5" W, 33.5" Dp.	1.5" x 6"	9-60W Cand. Base
ODL5206IB*	41" H, 18" W, 18" Dp.	1.5" x 6"	6-60W Cand. Base
ODL5303IB	16.5" H, 16" W, 16" Dp.	5"	3-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Fixtures come with 12' of wire and 8' of chain.

Opera COLLECTION

FINISH:
Western Bronze

NEW!
FOR ◆ 2016

DAMP **OPA5005WT**

OPA5304WT DAMP

NEW!
FOR ◆ 2016

FAUX PEARL ACCENTS

OPA1617WT DAMP

DAMP OPA1613WT

OperaCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
OPA1613WT	10" H, 13" W, 13" Dp.	8"	3-60W Cand. Base
OPA1617WT	10" H, 17.5" W, 17.5" Dp.	10"	4-60W Cand. Base
OPA5005WT	23.5" H, 22.5" W, 22.5" Dp.	5.5"	5-60W Cand. Base
OPA5304WT	17" H, 17" W, 17" Dp.	5.5"	4-60W Cand. Base

All chain-hung fixtures come with 8' of wire and 4' of chain.

Noble COLLECTION

FINISH:
Rustic Black

DAMP **NBE5009RK**

SOLID WOOD CANDLE HOLDERS

NBE5008RK

NBE8702RK

NBE5005RK

NBE5303RK

NobleCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
NBE5005RK*	25.5" H, 24" W, 24" Dp.	1" x 5"	-	5-60W Cand. Base
NBE5008RK*	31" H, 32" W, 32" Dp.	5"	-	8-60W Cand. Base
NBE5009RK**	36" H, 32" W, 32" Dp.	5"	-	9-60W Cand. Base
NBE5303RK*	19.5" H, 15" W, 15" Dp.	5"	-	3-60W Cand. Base
NBE8702RK	13" H, 11.5" W, 8" Dp.	5" x 5"	2.5"	2-60W Cand. Base

*Fixture comes with 8' of wire and 4' of chain.**Chain-hung fixture comes with 12' of wire and 8' of chain.

Sophia COLLECTION

FINISH:
BN Brushed Nickel
PN Palladian Bronze

GLASS:
etched Glass Painted White Inside

SPH5009BN DAMP

Sophia COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
SPH5009BN/PN	33.5" H, 32" W, 32" Dp.	5.75"	9-100W Med. Base **or** 23W CFL

Fixture comes with 12' of wire and 8' of chain.

From the **SOPHIA COLLECTION:**
SPH5009PN

Sophia COLLECTION

FINISH:
BN Brushed Nickel
PN Palladian Bronze

GLASS:
etched Glass Painted White Inside

SPH1508PN DAMP

Enlarged for detail

SPH5005PN DAMP

CLASSIC CONTEMPORARY CURVES

Sophia COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SPH1508BN/PN	5" H*, 8" W, 8" Dp.	5.75"	-	1-100W Med. Base **or** 23W CFL
SPH5005BN/PN	23" H, 26.5" W, 26.5" Dp.	5.5"	-	5-100W Med. Base **or** 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

NewHarborCOLLECTION

FINISH:
Western Bronze

DAMP **NHR1718WT**

DAMP **NHR5204WT**



NHR538WT DAMP

NewHarborCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
NHR1718WT	10.5" H, 18" W, 18" Dp.	4.75"	4-60W Vintage Bulbs Supplied
NHR5204WT†	23.5" H*, 14" W, 14" Dp.	5" Sq.	4-60W Vintage Bulbs Supplied
NHR538WT††	9.5" H**, 38" W, 12" Dp.	.75" x 4.75" x 9"	5-60W Vintage Bulbs Supplied

*Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods. †Fixture comes with 12' of wire. ††Fixture comes with 8' of wire.
Max Wattage: 100W Med. Base **or** 23W CFL.

Wilder COLLECTION

FINISH:
Mottled Black



DAMP **WLR5204MB**

WLR2820MB DAMP



DAMP WLR1506MB

DAMP WLR1716MB

Wilder COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
WLR1506MB	8.5" H*, 6" W, 6" Dp.	5"	1-60W Vintage Bulb Supplied
WLR1716MB	13.5" H, 16" W, 16" Dp.	5"	3-60W Vintage Bulbs Supplied
WLR2820MB†	24.5" H, 20.5" W, 20.5" Dp.	5"	4-60W Vintage Bulbs Supplied
WLR5204MB††	33" H, 16" W, 16" Dp.	5"	4-60W Vintage Bulbs Supplied

†Chain-hung fixture comes with 8' of wire and 4' of chain. ††Fixture comes with 12' of wire and 8' of chain.
Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. Max Wattage: 100W Med Base **or** 23W CFL.

Tricia COLLECTION

FINISH:
Vintage Silver

TCA5009VP

TCA8701VP DAMP

DAMP TCA5006VP

TCA5004VP DAMP

Tricia COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TCA5004VP*	31.5" H, 21" W, 21" Dp.	7"	-	4-60W Cand. Base
TCA5006VP*	36" H, 27" W, 27" Dp.	7"	-	6-60W Cand. Base
TCA5009VP**	41.5" H, 31" W, 31" Dp.	7"	-	9-60W Cand. Base
TCA8701VP	24.5" H, 3" W, 6.5" Ext.	4.5" x 11.5"	9.5"	1-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.

UnionStation COLLECTION

FINISH:
Western Bronze

SHADE:
Metal Mesh

DAMP **UST5003WT**

UnionStation COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
UST5003WT	20" H, 28" W, 28" Dp.	5"	3-60W Vintage Bulb + 1-50W MR-16 - w/GU10 Base Shielded (Supplied)**

Chain-hung fixture comes with 8' of wire and 4' of chain.

From the **UNION STATION COLLECTION:** UST5003WT

UnionStation COLLECTION

FINISH:
Western Bronze

SHADE:
Metal Mesh

DAMP **UST1505WT**



UST6127WT

DAMP **UST1716WT**

UnionStation COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS	SHADE DIMS.
UST1505WT	8" H*, 5" W, 5" Dp.	5"	1-60W Vintage Bulb Supplied**	-
UST1716WT	11.5" H, 16" W, 16" Dp.	5.5"	3-60W Vintage Bulb Supplied**	-
UST6127WT	26.5" H, 15.5" W, 15.5" Dp.	-	1-60W Vintage Bulb Supplied**	15.5" x 15.5" x 9"

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
Max Wattage: 100W Med. Base **or 23W CFL.

LAKESIDE: LKE5204VG (p. 168)

Dining & Foyer and More!

QUOIZEL

Auburn COLLECTION

FINISH:
Rustic Black

QUOIZEL
NATURALS
WOOD

DAMP 50

ABN5024RK



Auburn COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ABN5024RK	45" H, 48" W, 48" Dp.	5.5"	24-60W Cand. Base

Chain-hung fixture comes with 12' of wire and 8' of chain.

From the **AUBURN COLLECTION:**
ABN5006RK

Auburn COLLECTION

FINISH:
Rustic Black

DAMP **ABN5012RK**

WALNUT STAIN HIGHLIGHTS

QUOIZEL
NATURALS
WOOD

ABN5006RK DAMP

Auburn COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ABN5006RK	28" H, 28" W, 28" Dp.	5"	6-60W Cand. Base
ABN5012RK*	31" H, 36" W, 36" Dp.	5"	12-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Comes with12' of wire and 8' of chain.

MirrenCOLLECTION

FINISH:
Imperial Bronze

DAMP **MRN5008IB**

DAMP **MRN5006IB**

DAMP **MRN5005IB**

MirrenCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MRN5005IB	18" H, 21" W, 21" Dp.	5"	5-60W Cand. Base
MRN5006IB	23" H, 28" W, 28" Dp.	5"	6-60W Cand. Base
MRN5008IB	28" H, 32" W, 32" Dp.	5"	8-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

CastleHill COLLECTION

FINISH:
Antique Nickel

NEW!
FOR ◆ 2016

DAMP **CTH5009AN**

detail

CTH5006AN DAMP

NEW! FOR ◆ 2016

DAMP CTH5003AN

DAMP CTH5204AN

CastleHill COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
CTH5003AN	20.5" H, 19" W, 19" Dp.	5"	3-60W Cand. Base
CTH5006AN	24.5" H, 25" W, 25" Dp.	5"	6-60W Cand. Base
CTH5009AN*	33" H, 31" W, 31" Dp.	5"	9-60W Cand. Base
CTH5204AN*	30" H, 16.5" W, 16.5" Dp.	5"	4-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Fixtures come with 12' of wire and 8' of chain.

VoyagerCOLLECTION

FINISH:
Malaga

DAMP **VYR5024ML**



VYR5012ML

VYR5008ML

VYR5006ML

Voyager COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
VYR5006ML*	26" H, 28" W, 28" Dp.	6"	6-60W Cand. Base
VYR5008ML*	28" H, 36" W, 20" Dp.	5"	8-60W Cand. Base
VYR5012ML**	36" H, 36" W, 36" Dp.	5"	12-60W Cand. Base
VYR5024ML**	52" H, 48" W, 48" Dp.	6"	24-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.

From the **CARRABELLE COLLECTION:**
QMC1199FR

CarrabelleCOLLECTION

FINISH:
French Bronze

DAMP **QMC1199FR**

DAMP **CRE5004FR**

OPTIC CRYSTAL

CarrabelleCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE	SHADE DIMS.
CRE5004FR	24" H, 24" W, 24" Dp.	5.5"	4-60W Cand. Base	Silver Organza Chiffon	7" x 21" x 24"
QMC1199FR	23.5" H, 18" W, 18" Dp.	5.5"	5-60W Cand. Base	-	-

Chain-hung fixtures come with 8' of wire and 4' of chain.

Wesley COLLECTION

FINISH:
Italian Fresco

WSY5012IF

DAMP **WSY5008IF**

DAMP **WSY5005IF**

Wesley COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
WSY5005IF*	27" H, 26" W, 26" Dp.	5"	5-60W Cand. Base
WSY5008IF*	30" H, 30" W, 30" Dp.	5.5"	8-60W Cand. Base
WSY5012IF**	36" H, 36" W, 36" Dp.	7"	12-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.

Estate COLLECTION

FINISH:
Imperial Bronze

NEW!
FOR ◆ 2016

EST5208IB

EST5204IB

EST5206IB

SWIRLED CAST IRON ARMS

Estate COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
EST5204IB	29.5" H, 13.5" W, 13.5" Dp.	5"	4-60W Cand. Base
EST5206IB	44.5" H, 19.5" W, 19.5" Dp.	5"	6-60W Cand. Base
EST5208IB	53.5" H, 26.5" W, 26.5" Dp.	5"	8-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain.

DUN5204GK DAMP

Dunn

FINISH: Grey Ash

NEW!
FOR ◆ 2016

DAMP DUN5203GK

Woodrow

FINISH: Rustic Black

QF1839RK DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
DUN5203GK	22.5" H, 13" W, 13" Dp.	5"	3-60W Cand. Base
DUN5204GK	27" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
QF1839RK	22" H, 12" W, 12" Dp.	5.5"	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain

Silhouette COLLECTION

FINISH:
Italian Fresco

SHADE:
Sliver Organza Chiffon

CRYSTAL TEARDROPS

SLT5006IF DAMP

SLT5004IF DAMP

DAMP SLT5303IF

Silhouette COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
SLT5004IF	28" H, 24" W, 24" Dp.	5.5" x 1"	4-60W Cand. Base	6.5" x 24" x 24"
SLT5006IF	33.5" H, 28" W, 28" Dp.	5.5" x 1"	6-60W Cand. Base	9" x 30" x 30"
SLT5303IF	24" H, 18" W, 18" Dp.	5.5" x 1"	3-60W Cand. Base	6" x 18" x 18"

Chain-hung fixtures come with 8' of wire and 4' of chain.

Belhaven COLLECTION

FINISH:
Vintage Gold

SHADE:
Mica Shade with Black trim

QUOIZEL
NATURALS
MICA

DAMP BHN5009VG

DAMP BHN5006VG

NEW!
FOR ◆ 2016

DAMP BHN5303VG

Belhaven COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BHN5006VG	23" H*, 27" W, 27" Dp.	5"	6-60W Cand. Base
BHN5009VG**	30" H*, 31" W, 31" Dp.	5"	9-60W Cand. Base
BHN5303VG	15.5" H*, 16.5" W, 16.5" Dp.	5"	3-60W Cand. Base

*Rod-hung fixtures come with 8' of wire. **Fixture comes with 12' of wire. All rod-hung fixtures come with (2) 6" and (2) 12" Rods.

From the **ALSTON COLLECTION:**
QMC404BO

Miramar

FINISH: Polished Chrome
GLASS: Crystal Glass Accents

NEW!
FOR ◆ 2016

MMR5303C DAMP

Majesty

FINISH: Vantage Gold

DAMP MJY5304VG

See matching semi-flush ***MJY1615VG*** *on page 296.*

Alston

FINISH: Bolivian Bronze

DAMP QMC404BO

PRODUCT	DIMENSIONS	CANOPY	BULBS
MJY5304VG	19" H, 12" W, 12" Dp.	5"	4-60W Cand. Base
QMC404BO*	21" H, 18" W, 18" Dp.	5"	4-60W Cand. Base
MMR5303C	19.5" H, 12.5" W, 12.5" Dp.	5"	3-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Comes with 12' of wire and 8' of chain.

QUOIZEL
NATURALS
ROPE

Bandelier

FINISH: Imperial Bronze

BDR5006IB DAMP

*See matching pendant **BDR2820IB** in the Quoizel Naturals section on page 238.*

QUOIZEL
NATURALS
WOOD

DAMP **WDM5005WT**

Wyndmoor

FINISH: Western Bronze

HAND FORGED ACCENTS

CP5006IB DAMP

Capri

FINISH: Imperial Bronze

*See matching pendant **CP2820IB** on page 268.*

PRODUCT	DIMENSIONS	CANOPY	BULBS
BDR5006IB	24" H, 26" W, 26" Dp.	5.5"	6-60W Cand. Base
CP5006IB	22" H*, 32" W, 16.5" Dp.	.75" x 5"	6-60W Cand. Base
WDM5005WT	30" H, 28" W, 28" Dp.	5"	5-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.
Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Ridge Manor

FINISH: Mottled Black

QF1820MB DAMP

Collins

FINISH: Masterpiece

DAMP **QF1402CMU**

Frontier

FINISH: Imperial Bronze

FTR5204IB DAMP

*See matching semi-flush **FTR1713IB** on page 288.*

PRODUCT	DIMENSIONS	CANOPY	BULBS
FTR5204IB	23.5" H*, 13" W, 13" Dp.	5"	4-60W Cand. Base
QF1402CMU	29.5" H, 16.5" W, 16.5" Dp.	5.5"	4-60W Cand. Base
QF1820MB	27" H, 18" W, 18" Dp.	6"	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain.
Rod-hung fixtures come with 12' of wire.*Comes with (2) 6" and (2) 12" Rods.

Celestial

FINISH: Brushed Nickel
GLASS: Opal Etched

DAMP **CLT5004BN**

*See matching semi-flush **CLT1714BN** on page 289.*

Kemper

FINISH: Brushed Nickel
GLASS: Etched Painted White Inside

DAMP **KPR5005BN**

DOWNLIGHT

DAMP **AML5005OZ**

NEW!
FOR ◆ 2016

*See matching pendant **AML2821OZ** on page 265.*

Amelia

FINISH: Old Bronze
GLASS: Etched Painted White Inside

PRODUCT	DIMENSIONS	CANOPY	BULBS
AML5005OZ	30" H, 28.5" W, 28.5" Dp.	1.5" x 5.75"	5-100W Med. Base **or** 23W CFL
CLT5004BN	16" H*, 25" W, 25" Dp.	5"	4-100W Med. Base **or** 23W CFL
KPR5005BN	18.5" H*, 25" W, 25" Dp.	6.5"	5-100W Med. Base **or** 23W CFL + 1-50W MR16 GU10 Shielded Supplied

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

SerenityCOLLECTION

FINISH:
Italian Fresco

DAMP **SER5009IF**

DAMP **SER5006IF**

DAMP **SER5004IF**

SerenityCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
SER5004IF*	24" H, 20" W, 20" Dp.	1.25" x 5"	4-60W Cand. Base
SER5006IF*	27.5" H, 26.5" W, 26.5" Dp.	1.25" x 5"	6-60W Cand. Base
SER5009IF**	34" H, 30" W, 30" Dp.	5"	9-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.

Majestic COLLECTION

FINISH: Brushed Nickel
GLASS: Crystal Accents

NEW!
FOR ◆ 2016

detail

DAMP **MJT5008BN**

NEW!
FOR ◆ 2016

MJT5006BN DAMP

CRYSTAL GLASS ACCENTS

DAMP MJT5004BN

Majestic COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MJT5004BN	19.5" H, 15" W, 15" Dp.	5"	4-60W Cand. Base
MJT5006BN	26.5" H, 22.5" W, 22.5" Dp.	5"	6-60W Cand. Base
MJT5008BN	31" H, 27.5" W, 27.5" Dp.	5"	8-60W Cand. Base + 1 -60 W Clear G9 Xenon

Chain-hung fixtures come with 8' of wire and 4' of chain.

HK5008TC

Holbrook

FINISH: tuscan Brown

QUOIZEL NATURALS WOOD

HK5005TC

QF1840RK

Planter

FINISH: Rustic Black

QUOIZEL NATURALS WOOD

PRODUCT	DIMENSIONS	CANOPY	BULBS
HK5005TC	14" H, 24" W, 24" Dp.	5.5"	5-60W Cand. Base
HK5008TC	19.5" H, 29" W, 29" Dp.	5.5"	8-60W Cand. Base
QF1840RK*	26" H, 12.5" W, 12.5" Dp.	5"	3-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Fixture comes with 12' of wire and 8" of chain.

Thornhill

FINISH: Marcado Black

DAMP **THL5006MK**

NEW!
FOR ◆ 2016

Pendant converts to Semi-Flush Mount

THL1718MK DAMP

Menlo

FINISH: Western Bronze

NEW!
FOR ◆ 2016

*See matching bath fixtures **MNO8602,3,4 IS** on page 357.*

MNO5006WT DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
MNO5006WT	14" H*, 28" W, 28" Dp.	5"	6-60W Vintage Bulbs Supplied**
THL1718MK	16.5" H, 18" W, 18" Dp.	5"	4-40W Vintage Bulbs Supplied†
THL5006MK	27" H, 26" W, 26" Dp.	5"	6-40W Vintage Bulbs Supplied†

Chain-hung fixtures come with 8' of wire and 4' of chain. All rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
Max Wattage: 100W Med Base **or 23W CFL. †Max Wattage: 60W Cand. Base.

Lakeside

FINISH: Vintage Gold
GLASS: Clear Water

NEW!
FOR ◆ 2016

LKE5204VG DAMP

Colton

FINISH: Western Bronze
GLASS: Antique Mercury

NEW!
FOR ◆ 2016

DAMP CTO5204WT

DAMP GCT5204WT

NEW!
FOR ◆ 2016

Grand Court

FINISH: Western Bronze
GLASS: Clear Beveled

PRODUCT	DIMENSIONS	CANOPY	BULBS
CTO5204WT	18" H*, 17" W, 17" Dp.	5.5"	4-60W Cand. Base
GCT5204WT	23.5" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
LKE5204VG	31.5" H, 15" W, 15" Dp.	5"	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain. Rod-hung fixture comes with 12' of wire. *Comes with (2) 6" and (2) 12" Rods

Sabrina

FINISH: Vintage Gold
GLASS: Beveled Crystal

NEW!
FOR ◆ 2016

DAMP **SRA5204VG**

Kayden

FINISH: Brushed Nickel
GLASS: Clear Seedy

QUOIZEL NATURALS WOOD

DAMP **KDN5004BN**

*See matching mini pendant **KDN1510BN** on page 280.*

DAMP **UNS5204IB**

Unison

FINISH: Imperial Bronze

NEW!
FOR ◆ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
KDN5004BN	18.5" H*, 19.5" W, 19.5" Dp.	5"	4-60W Cand. Base
SRA5204VG**	26" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
UNS5204IB†	26" H, 20" W, 20" Dp.	6"	4-60W Cand. Base

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
**Chain-hung fixture comes with 12' of wire and 8' of chain. †Chain-hung fixture comes with 8' of wire and 4' of chain.

PB5004TK

Pembroke

FINISH: tarnished Bronze

NEW!
FOR ◆ 2016

PB5008TK

QUOIZEL
NATURALS
ROPE

BGS5203RK

NEW!
FOR ◆ 2016

Burgess

FINISH: Rustic Black
GLASS: Mercury Glass

See matching semi-flush ***BGS1715RK*** *on page 288.*

PRODUCT	DIMENSIONS	CANOPY	BULBS
BGS5203RK	24.5" H, 15" W, 15" Dp.	5"	3-60W Cand. Base
PB5004TK	23" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
PB5008TK	32" H, 22.5" W, 22.5" Dp.	5"	8-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

ANR5010IB

Anchor

FINISH: Imperial Bronze

QUOIZEL NATURALS WOOD

ANR5006IB

Knotting

FINISH: **VG** Vintage Gold
WT Western Bronze

QF1829WT

Also available in Vintage Gold:
QF1829VG

PRODUCT	DIMENSIONS	CANOPY	BULBS
ANR5006IB*	24.5" H**, 22.5" W, 22.5" Dp.	5"	6-60W Vintage Bulb Supplied†
ANR5010IB*	27.5" H**, 28" W, 28" Dp.	5"	10-60W Vintage Bulb Supplied†
QF1829WT/VG††	22" H**, 18.5" W, 18.5" Dp.	4.75"	4-60W Vintage Bulb Supplied†

*Rod-hung fixture comes with 8' of wire. **Comes with (2) 6" and (2) 12" Rods. †Max Wattage: 100W Med. Base **or** 23W CFL.
††Rod-hung fixtures come with 12' of wire.

PLATINUM by QUOIZEL

From the **RIBBONS COLLECTION:**
RBN2823SG (p.189)

The Platinum Collection is an exciting platform of contemporary design – playful and dramatic expressions in lighting. This collection utilizes energy-efficient light sources like G9 and G4 (low-voltage) bulbs, creating a dramatic effect through the intensity of light which showcases the refractive qualities of cut crystal.

Bordeaux COLLECTION

FINISH:
Polished Chrome

GLASS:
BRX Clear Crystal
BRXA Amber Crystal NEW!

DAMP **BRX2818C**

detail

BEAUTIFULLY CUT CRYSTALS

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

- Dramatic lighting created by faceted crystal pendants
- Free of contaminant colors such as iron for clarity and purity allowing the light to radiate to its greatest potential
- Bulbs are positioned in the most strategic locations, maximizing the radiance of the light emanating through the crystal
- Highly polished mirrored chrome maximizes the reflectivity of the projected light
- The highest quality G4 and G9 bulbs create a great intensity of light

DAMP **BRX1619C**

DAMP **BRX1614C**

DAMP **BRXA1619C**

NEW!
FOR ◆ 2016

DAMP **BRXA1614C**

Bordeaux COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BRX1614C	8" H, 14" W, 14" Dp.	14"	4-40W Clear G9 Xenon Supplied
BRX1619C	8" H, 19.5" W, 19.5" Dp.	17.75" x 1"	5-40W Clear G9 Xenon Supplied
BRX2818C*	8" H, 17.5" W, 17.5" Dp.	4.75" x 1"	5-40W Clear G9 Xenon Supplied
BRXA1614C	8" H, 14" W, 14" Dp.	14"	4-40W Clear G9 Xenon Supplied
BRXA1619C	9" H, 20" W, 20" Dp.	17.75" x 1"	5-40W Clear G9 Xenon Supplied

*Fixture comes with 8" of wire.

Bordeaux COLLECTION

FINISH:
Polished Chrome

GLASS:
Clear Crystal

DAMP **BRX1626C**

BRX1611C DAMP

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

NEW!
FOR ◆ 2016

DAMP **BRX1620C**

Bordeaux COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BRX1611C	8" H, 12" W, 12" Dp.	9.75"	4-40W Clear G9 Xenon Supplied
BRX1620C	10.5" H, 20" W, 20" Dp.	17.25"	6-40W Clear G9 Xenon Supplied
BRX1626C	8.5" H, 25.5" W, 25.5" Dp.	23.5" x 1"	7-40W Clear G9 Xenon Supplied

PLATINUM CRYSTAL LEAF
PCCF2824C (p. 180)

Galaxy COLLECTION

FINISH:
Polished Chrome

DAMP **PCGX1817C**

DAMP 50 **PCGX1826C**

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

Galaxy COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCGX1817C*	38" H, 17.5" W, 17.5" Dp.	5.875"	5-50W , MR16 GU10 Shielded Supplied
PCGX1826C**	53" H, 26" W, 30" Dp.	5.875"	7-50W , MR16 GU10 Shielded Supplied

*Fixture comes with 8' of wire. **Fixture comes with 10' of wire.

PCCT1616C DAMP

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

Countess

FINISH: Polished Chrome

DAMP PCCT1623C

PCAX1714C DAMP

Alexa

FINISH: Polished Chrome
SHADE: Crystal

See matching bath products on page 195.

NEW!
FOR ◆ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCAX1714C	8.5" H, 14" W, 14" Dp.	1" x 6"	3-100W Med. Base **or** 23W CFL
PCCT1616C	8.5" H, 16.5" W, 16.5" Dp.	13.75"	9-20W Clear G4 XENON Supplied
PCCT1623C	8" H, 23" W, 23" Dp.	19.5"	18-20W Clear G4 XENON Supplied

Crowne

FINISH: Polished Chrome
GLASS: Crystal Acccents

DAMP **PCCR1717C**





NEW!
FOR ◆ 2016

Crystal Leaf

FINISH: Polished Chrome
GLASS: Crystal Acccents

DAMP **PCCF2824C**

PCAN2814C DAMP

Arena

FINISH: Polished Chrome
SHADE: Crystal-l ined Metal Bands

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCAN2814C*	10.5" H, 14" W, 14" Dp.	6"	6-20W Clear G4 XENON Supplied
PCCF2824C**	24" H, 24" W, 24" Dp.	1" x 7.5"	8-40W Clear G9 XENON Supplied
PCCR1717C	11" H, 16.5" W, 16.5" Dp.	4.75"	4-40W Clear G9 XENON Supplied

*Fixture comes with 6' of wire. **Fixture comes with 8' of wire.

Mercury

FINISH: Polished Chrome
SHADE: Metal with Crystal Drops

PCMY2818C

1,000's OF CRYSTAL DROPS

NEW!
FOR ◆ 2016

INDIVIDUAL CRYSTALS INSIDE CLEAR GLASS

Treasure

FINISH: Polished Chrome
GLASS: Clear

PCTS1503C

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

Shimmer

FINISH: Polished Chrome
GLASS: Studded Crystal

See matching bath products on page 194.

PCSR1716C

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCMY2818C	5.5" H, 18" W, 18" Dp.	1" x 5.5"	6-60W Clear G9 XENON Supplied
PCSR1716C	7" H, 18" W, 18" Dp.	6.75	3-40W Clear G9 XENON Supplied
PCTS1503C	6" H, 3" W, 3" Dp.	1" x 4.75"	1-25W Clear G9 XENON Supplied

All cable-hung fixtures come with 8' of wire.

PCVN2820C

Vision

FINISH: Polished Chrome
GLASS: Clear n oodle

NEW!
FOR ◆ 2016

PCVN1716C

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

PRN1614C

Paragon

FINISH: Polished Chrome

See matching bath products on page 193.

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCVN1716C	13" H, 16" W, 16" Dp.	1" x 5.5"	4-60W Clear G9 XENON Supplied
PCVN2820C	5.5" H*, 20.5" W, 20.5" Dp.	1" x 5.5"	5-60W Clear G9 XENON Supplied
PRN1614C	6" H, 14.5" W, 14.5" Dp.	-	4-40W Clear G9 XENON Supplied

Fixtures comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Highrise

FINISH: Polished Chrome

DAMP **PCHE1620C**

DAMP **PCHE1616C**

INTEGRATED LED
10 YEAR WARRANTY

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

Janelle

FINISH: Polished Chrome
GLASS: Frosted, Sandblasted inside
SHADE: o rganza with Silver Trim

LED CHART

	PCJL2820C	PCHE1616C	PCHE1620C
Lumens	3080	2040	1080
Total Watts	37W	24W	10.8W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3100K	3000K	3000K
Dimmable	No	Yes	Yes

ILLUMINATED CRYSTAL RING

DAMP **PCJL2820C**

PRODUCT	DIMENSIONS	CANOPY	LIGHT SOURCE/ BULB
PCHE1616C	11" H, 16" W, 16" Dp.	13.75"	See LED chart
PCHE1620C	12.5" H, 20" W, 20" Dp.	18"	See LED chart
PCJL2820C	14.5" H*, 20" W, 20" Dp.	5"	3-100W Med. Base **or** 23W CFL + Crystal Ring – See LED chart

Fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Ella

FINISH: Polished Chrome

AMBER GLASS & CRYSTAL DROPS

PCEL1616C DAMP

PCEL1623C DAMP

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

PCSP2823C DAMP

Superior

FINISH: Polished Chrome

PCSP1718C DAMP

BEVELED CRYSTAL RODS

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCEL1616C	14" H, 16.5" W, 16.5" Dp.	14"	9-20W Clear G4 XENON Supplied
PCEL1623C	18" H, 23" W, 23" Dp.	19.5"	18-20W Clear G4 XENON Supplied
PCSP1718C	15.5" H, 18" W, 18" Dp.	5"	4-40W Clear G9 XENON Supplied
PCSP2823C	23.5" H*, 23" W, 23" Dp.	6"	6-40W Clear G9 XENON Supplied

Fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

VLA1618C

INTRICATE CRYSTAL DETAIL

Valla

FINISH: Polished Chrome

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

VLA2820C

PRODUCT	DIMENSIONS	CANOPY	BULBS
VLA1618C	7.5" H, 18.5" W, 18.5" Dp.	13.75"	9-20W Clear G4 XENON Supplied
VLA2820C	10" H*, 20" W, 20" Dp.	1" x 4.75"	6-40W Clear G9 XENON Supplied

Fixtures comes with 10' of wire.

Ribbons COLLECTION

FINISH:
Crystal Chrome

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

RBN2831CRC DAMP

RBN2817CRC DAMP

DAMP RBN2823CRC

All Ribbons pendants (all finishes) convert to Semi-Flush Mounts

Playful swirls and crystal accents make Ribbons an elegant must for the distinguished home décor.

RBN1512CRC DAMP

RBN1616CRC DAMP

DAMP RBN1628CRC

DAMP RBN1622CRC

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

Ribbons COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RBN1512CRC	12" H, 12" W, 12" Dp.	1.5"	3-50W Clear G9 Xenon Supplied
RBN1616CRC	9.5" H, 18.5" W, 18.5" Dp.	4.75"	4-40W Clear G9 Xenon Supplied
RBN1622CRC	11" H, 22" W, 22" Dp.	5.75"	5-40W Clear G9 Xenon Supplied
RBN1628CRC	16" H, 27.5" W, 27.5" Dp.	8"	6-40W Clear G9 Xenon Supplied
RBN2817CRC	17" H, 17" W, 17" Dp.	4.75" x 1"	5-40W Clear G9 Xenon Supplied
RBN2823CRC	23" H, 23" W, 23" Dp.	4.75" x 1"	12-40W Clear G9 Xenon Supplied
RBN2831CRC	31" H, 31" W, 31" Dp.	4.75" x 1"	12-40W Clear G9 Xenon Supplied

Cable-hung fixtures come with 8' of wire.

Ribbons COLLECTION

FINISHES:

C Polished Chrome
MN Millenia
SG Satin Copper
W White l ustre
WT Western Bronze

All Ribbons pendants (all finishes) convert to Semi-Flush Mounts

detail

PLATINUM by QUOIZEL

RBN2831WT DAMP

RBN1512SG

RBN2817W

RBN1616WT

PLATINUM by QUOIZEL

RBN2823MN

RBN1622MN

RBN1628W

RibbonsCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RBN1512C/MN/SG/W/WT	12" H, 12" W, 12" Dp.	1.5"	3-50W Frosted G9 Xenon Supplied
RBN1616C/MN/SG/W/WT	8" H, 16.5" W, 16.5" Dp.	4.75"	4-40W Frosted G9 Xenon Supplied
RBN1622C/MN/SG/W/WT	11" H, 22" W, 22" Dp.	5.75"	5-40W Frosted G9 Xenon Supplied
RBN1628C/MN/SG/W/WT	16" H, 27.5" W, 27.5" Dp.	8"	6-40W Frosted G9 Xenon Supplied
RBN2817C/MN/SG/W/WT	17" H, 17" W, 17" Dp.	4.75" x 1"	5-40W Frosted G9 Xenon Supplied
RBN2823C/MN/SG/W/WT	23" H, 23" W, 23" Dp.	4.75" x 1"	12-40W Frosted G9 Xenon Supplied
RBN2831C/MN/SG/W/WT	31" H, 31" W, 31" Dp.	4.75" x 1"	12-40W Frosted G9 Xenon Supplied

Cable-hung fixtures come with 8' of wire.

NEW!
FOR ◆ 2016

PCAE1715C

Enlarged for detail

PCAE2820C

Abode

FINISH: Polished Chrome
SHADE: o uter: l aser-Cut Metal
inner: Clear o rganza with Grey Trim

PLATINUM by QUOIZEL

PCAY1722C

Array

FINISH: Polished Chrome
GLASS: etched

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
PCAE1715C	9.5" H, 15" W, 15" Dp.	4.75"	3-100W Med. Base **or** 23W CFL	-
PCAE2820C	18" H*, 20" W, 20" Dp.	5"	3-100W Med. Base **or** 23W CFL	15.5" x 5.5"
PCAY1722C	9" H , 22" W, 22" Dp.	1" x 4.75"	3-60W Cand. Base	-

Fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

As seen in Better Homes & Gardens LIGHTING Magazine

PLATINUM MERCURY PENDANT: PCMY2818C (p.181)

Stellar

FINISH: Polished Chrome
GLASS: etched, Painted White inside

DAMP **PCSL1616C**

PLATINUM by QUOIZEL

NEW!
FOR ◆ 2016

METAL OUTTER SHADE



Encompass

FINISH: Millenia
GLASS: o pal

DAMP **PCEC1820MN**

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCEC1820MN	24.5" H*, 20" W, 20" Dp.	1" x 4.75"	1-100W Med. Base **or** 23W CFL
PCSL1616C	4.5" H, 16" W, 16" Dp.	-	3-60W Med. Base **or** 13W CFL

Fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Paragon COLLECTION

FINISH:
Polished Chrome

*See matching flush mount **PRN1614C** on page 182.*

CRYSTAL STRANDS

DAMP **PRN8606C**

Enlarged for detail

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION



DAMP **PRN8604C**

DAMP **PRN8608C**

Paragon COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PRN8604C	4.5" H, 14.5" W, 4" Ext.	7" x 5"	2.5"	4-20W Clear G4 Xenon Supplied
PRN8606C	5" H, 21.5" W, 4" Ext.	7" x 5"	2.5"	6-20W Clear G4 Xenon Supplied
PRN8608C	5" H, 28.5" W, 4" Ext.	7" x 5"	2.5"	8-20W Clear G4 Xenon Supplied

Shimmer COLLECTION

FINISH:
Polished Chrome

GLASS:
Crystal Studded

PCSR8603CLED

Enlarged for detail

See matching semi-flush ***PCSR1716C*** *on page 181.*

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

MOUNTS

PCSR8602CLED

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

PCSR8604CLED

Shimmer COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSR8602CLED	8" H, 13.5" W, 5.5" Ext.	4.75" x 4.75"	6"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSR8603CLED	8" H, 23" W, 5.5" Ext.	4.75" x 4.75"	6"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSR8604CLED	8" H, 32" W, 5.5" Ext.	4.75" x 4.75"	6"	4-4.5W Frosted G9 LED Dimmable Supplied

Shimmer bath fixtures can be mounted as uplights or downlights.

Alexa

FINISH: Polished Chrome
GLASS: Crystal

See matching semi-flush ***PCAX1714C*** *on page 179.*

PCAX8603CLED DAMP

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **PCAX8604CLED**

PCED8517C DAMP

Enlarged for detail

INTEGRATED LED
10 YEAR WARRANTY

MOUNTS

DAMP **PCED8528C**

Endless

FINISH: Polished Chrome
GLASS: o ptic, Sandblasted inside

DAMP **PCED8521C**

LED CHART

	PCED8517	PCED8521	PCED8528
Lumens	1200	1800	2500
Total Watts	12W	18W	25W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3000K	3000K	3000K
Dimmable	Yes	Yes	Yes

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS/LIGHT SOURCE
PCAX8603CLED	5" H, 25" W, 4" Ext.	24.37" x 5.12"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
PCAX8604CLED	5" H, 33" W, 4" Ext.	32.25" x 5.12"	3"	4-4.5W Frosted G9 LED Dimmable Supplied
PCED8517C	4.5" H, 17.5" W, 4.5" Ext.	17.37" x 4.37"	2.18"	See LED chart
PCED8521C	4.5" H, 21.5" W, 4.5" Ext.	21.25" x 4.37"	2.18"	See LED chart
PCED8528C	4.5" H, 29" W, 4.5" Ext.	28.75" x 4.37"	2.18"	See LED chart

PLATINUM VISION PENDANT:
PCVN2820C (p. 182)

Evermore COLLECTION

FINISH: Polished Chrome
SHADE: Crystal

DAMP **EME8604C**

Enlarged for detail

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

FACETED CRYSTALS

DAMP **EME8606C**

DAMP **EME8608C**

Evermore COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
EME8604C	5" H, 16" W, 6" Ext.	7" x 4.5"	2.5"	4-20W Clear G4 Xenon Supplied
EME8606C	5" H, 23.5" W, 6" Ext.	7" x 4.5"	2.5"	6-20W Clear G4 Xenon Supplied
EME8608C	5" H, 31" W, 6" Ext.	7" x 4.5"	2.5"	8-20W Clear G4 Xenon Supplied

Pierre

FINISH: Brushed n ickel
GLASS: o ptic

INTEGRATED LED
10 YEAR WARRANTY

MOUNTS MOUNTS

DAMP **PCPR8522BN** *Enlarged for detail*

LED CHART

	PCPR8522	PCPR8530
Lumens	1800	2200
Total Watts	20W	28W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

DAMP **PCPR8530BN**

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

FACETED CRYSTALS

DAMP **RYE8604C** *Enlarged for detail*

DAMP **RYE8605C**



Royale

FINISH: Polished Chrome

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS/LIGHT SOURCE
PCPR8522BN	4.5" H, 22" W, 4" Ext.	4.5" x 7"	2.5"	See LED chart
PCPR8530BN	4.5" H, 30" W, 4" Ext.	4.5" x 7"	2.5"	See LED chart
RYE8604C	5" H, 20" W, 5" Ext	7" x 4.5"	2.5"	4-20W Clear G4 Xenon Supplied
RYE8605C	5" H, 24" W, 5" Ext	7" x 4.5"	2.5"	5-20W Clear G4 Xenon Supplied

Seaview COLLECTION

NEW!
FOR ◆ 2016

FINISH: BN Brushed n ickel **C** Polished Chrome
GLASS: BN Clear Thick **C** Clear Thick etched inside

DAMP PCSW8602CLED

Enlarged for detail

MOUNTS

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

PLATINUM by QUOIZEL

PCSW8601BNLED DAMP

DAMP PCSW8603BNLED

PCSW8604CLED DAMP

Seaview COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSW8601BNLED / CLED	7" H, 5.5" W, 4.5" Ext.	4.75" x 7"	4"	1-4.5W Frosted G9 LED Dimmable Supplied
PCSW8602BNLED / CLED	5.5" H, 14.5" W, 5" Ext.	7" x 4.75"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSW8603BNLED / CLED	5.5" H, 22" W, 5" Ext.	7" x 4.75"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSW8604BNLED / CLED	5.5" H, 30" W, 5" Ext.	7" x 4.75"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Seaview bath fixtures can be mounted as uplights or downlights.

Serena COLLECTION

NEW!
FOR ◆ 2016

FINISH: Brushed n ickel
GLASS: Clear

DAMP **PCSA8602BNLED**

Enlarged for detail

MOUNTS

PLATINUM by QUOIZEL

DAMP **PCSA8603BNLED**

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **PCSA8604BNLED**

Serena COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSA8602BNLED	6.5" H, 12.5" W, 5.5" Ext.	6.75" x 4.75"	5.12"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSA8603BNLED	6.5" H, 20" W, 5.5" Ext.	6.75" x 4.75"	5.12"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSA8604BNLED	6.5" H, 28" W, 5.5" Ext.	6.75" x 4.75"	5.12"	4-4.5W Frosted G9 LED Dimmable Supplied

Serena bath fixtures can be mounted as uplights or downlights.

Lacombe

FINISH: Polished Chrome
SHADE: Metal Frame with Clear Glass Beads

NEW!
FOR ◆ 2016

DAMP PCLC8603CLED

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

DAMP PCLC8605CLED

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

DAMP PCMR8603CLED

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

DAMP PCMR8605CLED

Mirabella

NEW!
FOR ◆ 2016

FINISH: Polished Chrome
GLASS: Crystal Accents

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCLC8603CLED	5" H, 18" W, 5.5" Ext.	14.5" x 4.75"	2.5"	3-4.5W Frosted G9 LED Dimmable Supplied
PCLC8605CLED	5" H, 26" W, 6.5"" Ext.	19.5" x 4.75"	2.5"	5-4.5W Frosted G9 LED Dimmable Supplied
PCMR8603CLED	9.5" H, 12" W, 5.5" Ext.	12" x 6"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
PCMR8605CLED	11" H, 24" W, 6" Ext.	24" x 6"	3"	5-4.5W Frosted G9 LED Dimmable Supplied

Lacombe and Mirabella bath fixtures can be mounted as uplights or downlights.

Divine COLLECTION

FINISH: Polished Chrome
GLASS: Clear Crystal

DAMP **PCDV8602CLED**

detail

NEW!
FOR ◆ 2016

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

MOUNTS

PCDV8603CLED DAMP

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **PCDV8604CLED**

Divine COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCDV8602CLED	6" H, 13.5" W, 6" Ext.	7" x 4.75"	5.25"	2-4.5W Frosted G9 LED Dimmable Supplied
PCDV8603CLED	6" H, 23" W, 6" Ext.	7.5" x 4.75"	5.25"	3-4.5W Frosted G9 LED Dimmable Supplied
PCDV8604CLED	6" H, 31.5" W, 6" Ext.	7.5" x 4.75"	5.25"	4-4.5W Frosted G9 LED Dimmable Supplied

Divine bath fixtures can be mounted as uplights or downlights.

PCDH8522BN

PCDH8530BN

Dash

FINISH: Brushed n ickel
GLASS: White

LED CHART

	PCDH8522BN	PCDH8530BN
Lumens	1600	2240
Total Watts	20W	28W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

MOUNTS

INTEGRATED LED
10 YEAR WARRANTY

PCGL8522BN

Enlarged for detail

Glacial

FINISH: Brushed n ickel
GLASS: Clear with Sandblast inside

MOUNTS

LED CHART

	PCGL8522BN	PCGL8530BN
Lumens	1700	3200
Total Watts	22W	30W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Dimmable	Yes	Yes

PCGL8530BN

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCDH8522BN	4.5" H, 22" W, 3.5" Ext.	21.5" x 4.5"	2.5"	See LED chart
PCDH8530BN	4.5" H, 30" W, 3.5" Ext.	29.5" x 4.5"	2.5"	See LED chart
PCGL8522BN	5" H, 22" W, 5" Ext.	6" x 5"	2.5"	See LED chart
PCGL8530BN	5.5" H, 30" W, 5" Ext.	6.75" x 5.5"	2.5"	See LED chart

Valiant

NEW! FOR ◆ 2016

FINISH: Brushed Nickel
GLASS: Clear Etched Inside



DAMP **PCVT8518BN**

Enlarged for detail

MOUNTS

DAMP **PCVT8524BN**

LED CHART

	PCVT8518BN	PCVT8524BN
Lumens	1565	2020
Total Watts	21W	39W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

PLATINUM by QUOIZEL

INTEGRATED LED

10 YEAR WARRANTY

Blade

NEW! FOR ◆ 2016

FINISH: Polished Chrome
GLASS: Opal Etched

DAMP **PCBD8519C**

MOUNTS

LED CHART

	PCBD8526C	PCBD8519C
Lumens	2565	1830
Total Watts	33W	25W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	2700K	2700K
Dimmable	Yes	Yes

DAMP **PCBD8526C**

Enlarged for detail

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCBD8519C	5" H, 19" W, 4.5" Ext .	4.75" x 6.75"	2.5"	See LED chart
PCBD8526C	5" H, 26" W, 4.5" Ext.	4.75" x 6.75"	2.5"	See LED chart
PCVT8518BN	5" H, 18" W, 3.5" Ext.	4.5" x 5.75"	2.5"	See LED chart
PCVT8524BN	5" H, 24" W, 3.5" Ext.	4.5" x 5.75"	2.5"	See LED chart

Valiant and Blade bath fixtures can be mounted as horizontally or vertically.



Pace

FINISH: Polished Chrome
GLASS: Opal Etched Inner, Clear Outer

PCPC8527C DAMP

Enlarged for detail

DAMP **PCPC8533C**

LED CHART

	PCPC8527C	PCPC8533C
Lumens	2060	2740
Total Watts	32W	42W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

PLATINUM by QUOIZEL

INTEGRATED LED
10 YEAR WARRANTY



Promenade

FINISH: Polished Chrome
GLASS: Acrylic Rectangular

MOUNTS MOUNTS

PCPE8524C DAMP

Enlarged for detail

LED CHART

	PCPE8524C	PCPE8536C
Lumens	960	1440
Total Watts	8W	12W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

PCPE8536C DAMP

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCPC8527C	4.5" H, 26.5" W, 4" Ext.	7" x 4.5"	2.5"	See LED chart
PCPC8533C	4.5" H, 33" W, 4" Ext.	7" x 4.5"	2.5"	See LED chart
PCPE8524C	4.5" H, 24" W, 3" Ext.	7" x 4.5"	2.5"	See LED chart
PCPE8536C	4.5" H, 37" W, 3" Ext.	7" x 4.5"	2.5"	See LED chart

Bram COLLECTION

FINISH: Polished Chrome
GLASS: o pal etched

NEW!
FOR ◆ 2016



PCBM8520C DAMP

Enlarged for detail

PLATINUM by QUOIZEL

INTEGRATED LED
10 YEAR WARRANTY



DAMP **PCBM8526C**

OPTIC GLASS

PCBM8505C DAMP

LED CHART

	PCBM8505C	PCBM8520C	PCBM8526C
Lumens	880	2138	2996
Total Watts	12W	25.5W	36W
Color Rendering Index (CRI)	90	90	90
Color Temperature (CCT)	2700K	3000K	3000K
Dimmable	Yes	Yes	Yes

Bram COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCBM8505C	13.5" H, 5.5" W, 3.5" Ext.	4.5" x 4.5"	8.75"	See LED chart
PCBM8520C	5.5" H, 20.5" W, 3.5" Ext.	4.5" x 4.5"	3"	See LED chart
PCBM8526C	5.5" H, 26.5" W, 3.5" Ext.	4.5" x 4.5"	3"	See LED chart

Bram bath fixtures can be mounted as horizontally or vertically.

Designer showCase

Carolyn Kinder

QUOIZEL

For nearly four decades, **Carolyn Kinder** has been designing and developing innovative collections for the home furnishings industry. Carolyn has an established reputation that has become synonymous with class and timeless design.

With roots in the heartland of America, Kinder travels the globe, discovering and developing sources to deliver rich textures, layered finishes and unique raw materials.

Scan with your smart phone **or** *tablet to view an informative video relating to the Carolyn Kinder Collection by Quoizel!*

From the **CAROLYN KINDER CONFETTI COLLECTION:** CKCF2822OS (p. 209)

Photo courtesy of Kenorah Design & Build Ltd.

Confetti COLLECTION

FINISH:
OS o ld s ilver **RK** r ustic Black NEW!

SHADE:
inner: o ff-White Linen
o uter: Metal Confetti

NEW!
FOR ◆ 2016

DAMP CKCF339RK

CKCF6330OS

Carolyn Kinder INTERNATIONAL

CKCF43624OS

DAMP CKCF2825OS

NEW!
FOR ◆ 2016

CKCF2822RK DAMP

CKCF1717RK DAMP

NEW!
FOR ◆ 2016

DAMP CKCF1720OS

DAMP CKCF1714OS

NEW!
FOR ◆ 2016

CKCF1508RK DAMP

NEW!
FOR ◆ 2016

Carolyn Kinder INTERNATIONAL

DAMP CKCF2816RK

Confetti COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
CKCF1508OS/RK	9" H*, 8" W, 8" Dp.	5.5"	1-100W Med. Base **or** 23W CFL	-
CKCF1714OS	11.5" H, 14" W, 14" Dp.	5.5"	2-100W Med. Base **or** 23W CFL	5.5" x 13" x 13"
CKCF1717OS/RK	11.5" H, 17" W, 17" Dp.	5.5"	3-100W Med. Base **or** 23W CFL	5.5" x 16" x 16"
CKCF1720OS	11.5" H, 20" W, 20" Dp.	5.5"	4-100W Med. Base **or** 23W CFL	5.5" x 19" x 19"
CKCF2816OS/RK	10" H*, 16" W, 16" Dp.	5.5"	3-100W Med. Base **or** 23W CFL	-
CKCF2822OS/RK	10.5" H*, 22" W, 22" Dp.	5.5"	4-100W Med. Base **or** 23W CFL	-
CKCF2825OS/RK	10" H*, 25" W, 25" Dp.	5.5"	5-100W Med. Base **or** 23W CFL	9.5" x 24" x 24"
CKCF3390S/RK	9" H**, 39.5" W, 8" Dp.	.75" x 4.5"	3-100W Med. Base **or** 23W CFL	-
CKCF436240S	35" H, 24" W, 1" Dp.	-	-	-
CKCF6330OS	29.5" H, 8" W, 14" Dp.	-	2-75W Med. Base **or** 18W CFL	Fabric Inner Shade: (8.5" x 13") x (7" x 13") x 7" Metal Outer Shade: (8"x14") x (8"x14") x 9"

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
**Comes with (6) 6" and (6) 12" Rods.

Metro COLLECTION

FINISH:
Brushed n ickel

SHADE:
Khaki Linen with silver Liner

Carolyn Kinder INTERNATIONAL

CKMO2820BN

CKMO1716BN

CKMO5003BN

INNER OPAL ETCHED GLASS

Metro COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.	GLASS
CKMO1716BN	11" H, 15.5" W, 15.5" Dp.	6"	2-60W Med. Base **or** 13W CFL	15.5" x 6"	-
CKMO2820BN	8" H*, 20" W, 20" Dp.	6"	3-100W Med. Base **or** 23W CFL	20" x 7"	-
CKMO5003BN	33" H, 33.5" W, 33.5" Dp.	6"	3-100W Med. Base **or** 23W CFL	Outer: 10" x 6.5"	Opal Etched

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixture comes with 8' of wire. *Comes with 2 (6)" and (2) 12" Rods.

From the **CAROLYN KINDER METRO COLLECTION:**
CKMO5003BN

Brookmont

tan Hardback Fabric Shade

CKBT1863T

Sanctuary

FINISH: Driftwood
GLASS: Clear Seedy

NEW! FOR ◆ 2016

CKSC5201DR DAMP

QUOIZEL NATURALS WOOD

Carolyn Kinder INTERNATIONAL

Hickman

tan linen Fabric Shade
with Self trim top and Bottom

CKHM1879T

MIRRORED FRAME

Ultra

Beveled Mirror

CKUT1921

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE
CKBT1863T	27" H, 18" W, 9" Dp.	-	1-150W Med. Base (3-way) **or** 40W CFL	(9" x 18") x (9" x 18") x 9"
CKHM1879T	34" H, 16" W, 16" Dp.	-	2-60W Med. Base **or** 13W CFL	6" x 16" x 16"
CKSC5201DR	30" H, 18.5" W, 18.5" Dp.	5.5"	1-100W Med. Base **or** 23W CFL	-
CKUT1921	36" H, 24" W, 2" Dp.	-	-	-

Chain-hung fixture comes with 8' of wire and 4' of chain.

Marisol COLLECTION

FINISH:
teco Marrone

SHADE:
inner: Beige h ardback Linen
o uter: o pen strap Metal

DAMP CKMS2822TM

Carolyn Kinder INTERNATIONAL

DAMP CKMS1716TM

CKMS442TM DAMP

Marisol COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
CKMS1716TM	12" H, 16" W, 16" Dp.	6" x 0.75"	3-100W Med. Base **or** 23W CFL	14.5" x 6.5"
CKMS2822TM	30" H, 22" W, 22" Dp.	6"	4-100W Med. Base **or** 23W CFL	19" x 8"
CKMS442TM	32.5" H, 42" W, 11" Dp.	9.75" x 5"	5-100W Med. Base **or** 23W CFL	8.5" x 39.5" x 8"

All chain-hung fixtures come with 8' of wire and 4' of chain.

CAROLYN KINDER KENDRICK MINI PENDANTS:
CKKD1509WT

Kendrick

FINISH: Western Bronze
GLASS: Moon h aze

NEW!
FOR ◆ 2016

CKKD1509WT DAMP

Nikos

FINISH: Burnished s ilver



DAMP CKNK1509BV

MIRRORED MERCURY GLASS

Sonia

FINISH: Artica

CKSN1507AR DAMP

DAMP CKGN1509MZ

Gaston

FINISH: Mottled Bronze

Carolyn Kinder INTERNATIONAL

PRODUCT	DIMENSIONS	CANOPY	BULBS
CKGN1509MZ**	10.5" H, 9" W, 9" Dp.	5.5"	1-100W Med. Base **or** 23W CFL
CKKD1509WT*	19" H, 9.5" W, 9.5" Dp.	1" x 5.5"	1-100W Med. Base **or** 23W CFL
CKNK1509BV*	14" H, 9" W, 9" Dp.	5.5"	1-60W Vintage Bulb Supplied†
CKSN1507AR**	10.5" H, 7.5" W, 7.5" Dp.	5.5"	1-100W Med. Base **or** 23W CFL

*Fixtures come with 8' of cable. **Fixtures come with 10' of cable. †Max Wattage: 100W Med. Base **or** 23W CFL.

Designer showCase

QUOIZEL

UPTOWN by Sergio Orozco

UPTOWN by SERGIO OROZCO NEW YORK

From the **UPTOWN EAST VILLAGE COLLECTION: UPEV8701WT**

New York City is the epicenter of American fashion. t he Uptown Collection by sergio o rozco for Quoizel captures the eclectic fashion pulse witnessed on the streets of this energetic city and reinterprets it for homeowners who appreciate designs that are fresh, cutting edge and yet comfortably liveable.

Born and raised in Columbia and educated in europe, sergio o rozco has received numerous awards for his lighting designs. n ow this Manhattan-based designer brings his global perspective to Quoizel's Uptown Collection, a unique design that can enhance an eclectic mix of home styles anywhere in the country.

Scan with your smart phone **or** *tablet to view an informative video relating to the Uptown Collection by Segio Orozco for Quoizel!*

UPTOWN by SERGIO OROZCO NEW YORK

UPEV5005WT DAMP

East Village

FINISH: Western Bronze
GLASS: Clear



DAMP UPEV8701WT

Enlarged for detail

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
UPEV5005WT	20" H*, 26" W, 26" Dp.	6.5"	-	5-40W Vintage Bulb Supplied**
UPEV8701WT	11" H, 6.5" W, 5" Ext	6.5" x 6.5"	8"	1-40W Vintage Bulb Supplied**

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 60W Med. Base **or** 13W CFL

TheaterRow COLLECTION

UPTOWN by SERGIO OROZCO NEW YORK

FINISH:

IS imperial silver
WT Western Bronze

UPTR1716WT DAMP

VINTAGE STYLE
bulb included

UPTR5007WT DAMP

ADA APPROVED

DAMP **UPTR8701IS**

TheaterRow COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
UPTR1716WT	6.5" H, 17.5" W, 17.5" Dp.	6"	-	4-60W Vintage Bulb Supplied†
UPTR5007WT	29" H*, 28" W, 28" Dp.	6.5"	-	6-60W Vintage Bulb + 1-50W MR-16 with GU10 Base Shielded Supplied†
UPTR8701IS/WT	10" H, 10" W, 4" Dp.	5.5" Sq.	6.5"	1-60W Vintage Bulb Supplied†

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
†Max Wattage: 100W Med. Base **or** 23W CFL.

Ritz COLLECTION

UPTOWN by SERGIO OROZCO NEW YORK

FINISH: Polished Chrome
GLASS: Beveled

UPRZ53426C

UPRZ43426C

Ritz COLLECTION

PRODUCT	DIMENSIONS
UPRZ43426C	34" H, 26" W, 2" Dp.
UPRZ53426C	34" H, 26" W, 2" Dp.

From the **UPTOWN CARNEGIE COLLECTION:**
UPCN5006WT

UPTOWN by SERGIO OROZCO NEW YORK

FINISH:
IS imperial silver
WT Western Bronze

UPCN5008WT DAMP

UPCN5006IS DAMP

Carnegie COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
UPCN5006IS/WT	22.5" H*, 25.5" W, 25.5" Dp.	6.5" x 1"	6-60W Vintage Bulb (Supplied)**
UPCN5008IS/WT	30" H*, 34" W, 34" Dp.	6.5"	8-60W Vintage Bulb (Supplied)**

Rod-hung fixtures come with 8' of wire. *Comes with 2 (6)" and (2) 12" Rods. **Max Wattage: 100W Med. Base **or** 23W CFL

MadisonManor COLLECTION

FINISH: Western Bronze
SHADE: Light Beige Fabric

UPTOWN by SERGIO OROZCO NEW YORK

UPMM8701WT DAMP

UPMM5005WT DAMP

MadisonManor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
UPMM5005WT	25.5" H*, 32" W, 32" Dp.	6.5"	-	5-75W Frosted G9 Halogen Supplied	4" x 7.5" x 8.5"
UPMM8701WT	20" H, 8.5" W, 9" Ext.	6.5" x 6.5"	10.5	1-75W Frosted G9 Halogen Supplied	4" x 8.5" x 7.5"

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

From the **UPTOWN MADISON MANOR COLLECTION**
Hanging Fixture: **UPMM5005WT** Wall Fixture: **UPMM8701WT**

UPTOWN
by SERGIO OROZCO
NEW YORK

Columbus Circle

FINISH: imperial Silver
GLASS: o pal etched

UPCC5006IS DAMP

INGENIOUS DESIGN MOTIF

Fulton

FINISH: imperial Silver
GLASS: o pal etched

DAMP **UPFT1820IS**

PRODUCT	DIMENSIONS	CANOPY	BULBS
UPCC5006IS††	26" H*, 28" W, 28" Dp.	6.5"	6-75W Frosted G9 Halogen Supplied
UPFT1820IS†	10.5" H**, 20" W, 20" Dp.	6"	3-100W Med. Base **or** 23W CFL

*Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods. †Fixture comes with 10' of wire. ††Fixture comes with 12' of wire.

PennStation COLLECTION

UPTOWN by SERGIO OROZCO NEW YORK

FINISH:
BN Brushed n ickel **WT** Western Bronze

GLASS:
Clear



DAMP **UPPS1510WT**

DAMP **UPPS1713BN**

DAMP **UPPS2813BN**

PennStation COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
UPPS1510BN/WT**	17" H*, 10" W, 10" Dp.	6.5"	1-60W Vintage Bulb Supplied††
UPPS1713BN/WT	10.5" H, 13" W, 13" Dp.	6.5"	1-60W Vintage Bulb Supplied††
UPPS2813BN/WT***	23.5" H*, 13" W, 13" Dp.	6.5"	3-40W T8 Vintage Bulb Supplied†

*Comes with (2) 6" and (2) 12" Rods. **Rod-hung fixtures come with 10' of wire. ***Fixture comes with 12' of wire.
†Max Wattage: 60W Cand. Base. ††Max Wattage: 100W Med. Base **or** 23W CFL.

UPTOWN
by SERGIO OROZCO
NEW YORK

UPSE8701WT

Enlarged for detail

Seaport

FINISH: Western Bronze

INNOVATIVE OPTIC GLASS

ON/OFF SWITCH

UPHL8701IS

Holita

FINISH: imperial silver
SHADE: Light Beige Fabric

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS	SHADE
UPHL8701IS	50" H, 12" W, 6" Ext.	5" x 8"	14"	1-60W Med. Base **or** 13W CFL	12.5" x 5.5" x 8"
UPSE8701WT	15" H, 4.5" W, 5" Ext.	6.5" x 6.5"	7"	1-40W T8 Vintage Bulb Supplied*	-

*Max Wattage: 60W Cand. Base

QUOIZEL NATURALS

Scan with your smart phone or tablet to view an informative video relating to Quoizel Naturals products!

From the **KYLE COLLECTION: KY6328IB** (p.73)

Color in Quoizel Naturals products may vary from images shown because of variations in natural materials.

Laguna COLLECTION

FINISH:
Renaissance Copper

SHADE:
Oyster Mica & Mosaic Tile

Pendant converts to Semi-Flush Mount

DAMP **MC8420CRC**

DAMP **MC842CRC**

QUOIZEL
NATURALS
MICA

MC842SRC

MCLG1616RC

MCLG1612RC

MC842FRC

MC842TRC

Enlarged for detail

QUOIZEL NATURALS MICA

Laguna COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
MC842CRC††	6.5" H*, 16" W, 16" Dp.	5"	3-60W Med. Base **or** 13W CFL	16" x 6"
MC842FRC	60" H, 16" W, 16" Dp.	-	2-60W Med. Base **or** 13W CFL	16" x 7.5"
MC842SRC	12" H, 16" W, 16" Dp.	5"	3-60W Med. Base **or** 13W CFL	16" x 6"
MC842TRC	25" H, 16" W, 16" Dp.	-	2-60W Med. Base **or** 13W CFL	16" x 7.5"
MC8420CRC†	5.5" H*, 22" W, 22" Dp.	5"	4-60W Med. Base **or** 13W CFL	22" x 6"
MCLG1612RC	5.5" H, 12" W, 12" Dp.	12"	2-60W Med. Base **or** 13W CFL	12" x 4"
MCLG1616RC	5.5" H, 16" W, 16" Dp.	16"	3-60W Med. Base **or** 13W CFL	16" x 4.5"

†Rod-hung fixture comes with 8' of wire. ††Fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

From the **LAGUNA COLLECTION:**
Mini Pendant: **MC842PRC** Pendants: **MC842CRC**
Photo Courtesy of Devane Design

Laguna COLLECTION

FINISH:
Renaissance Copper

SHADE:
Oyster Mica & Mosaic Tile

Q4574A

NEW!
FOR ◆ 2016

MC842PRC

QUOIZEL
NATURALS
MICA

MCLG337RC

Laguna COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
MC842PRC†	7.5" H*, 6" W, 6" Dp.	5"	1-60W Med. Base **or** 13W CFL	6" x 8"
MCLG337RC††	21" H**, 37" W, 16" Dp.	7.5" x 4.5"	3-100W Med. Base **or** 23W CFL	37" x 16" x 8"
Q4574A	76" H, 56.5" W, 16" Dp.	-	1-150W Med. Base or 40W CFL	-

†Rod-hung fixture comes with 10' of wire. ††Fixture comes with 12' of wire. *Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods.

NEW!
FOR ◆ 2016

MC2042T

Prism
SHADE: Mica

NEW!
FOR ◆ 2016

MCAL9470IB

MC1862TIB

Enlarged for detail

Alistar
FINISH: imperial Bronze
GLASS: Tiffany & Oyster Mica

QUOIZEL
NATURALS
MICA

PRODUCT	DIMENSIONS	BULBS	
MC1862TIB	23" H, 15" W, 9" Dp.	2-60W Med. Base **or** 13W CFL	Contains 20 Pieces of Tiffany & Mica
MC2042T	25" H, 15.5" W, 15.5" Dp.	2-60W Med. Base or 13W CFL	-
MCAL9470IB	70" H, 15" W, 9.5" Dp.	2-60W Med. Base or 13W CFL	Contains 20 Pieces of Tiffany & Mica



PULL-CHAIN

San Gabriel

FINISH: Valiant Bronze
GLASS: Mica & Tiffany

NX615TVA

QUOIZEL
NATURALS
MICA

Cyrus

FINISH: Anniversary Silver
GLASS: Oyster Mica & Tiffany Glass

MCCS6326AS

MCCS9357AS



MCCS9470AS

PRODUCT	DIMENSIONS	BULBS	
MCCS6326AS	25.5" H, 19.5" W, 19.5" Dp.	2-60W Med. Base **or** 13W CFL	Contains 144 pieces of Oyster Mica & Tiffany Glass
MCCS9357AS	57.5" H, 19.5" W, 19.5" Dp.	2-60W Med. Base **or** 13W CFL	Contains 144 pieces of Oyster Mica & Tiffany Glass
MCCS9470AS	70" H, 19.5" W, 19.5" Dp.	1-150W Med. Base **or** 40W CFL	Contains 144 pieces of Oyster Mica & Tiffany Glass
NX615TVA	23.5" H, 14.5" W, 14.5" Dp.	2-60W Med. Base **or** 13W CFL + 17W Cand. Base Supplied	Contains 176 pieces of Mica & Tiffany Glass

Kingsford

FINISH: Teco Marrone
SHADE: Oyster Mica

Pendant converts to Semi-Flush Mount

MCKD1505TM DAMP

MCKD2819TM DAMP

DAMP **MCKD1715TM**

QUOIZEL NATURALS MICA

Morrow

FINISH: Mottled Silver
SHADE: Mica

DAMP **MC1910MM**

Pendant converts to Semi-Flush Mount

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
MC1910MM	8.5" H*, 18" W, 18" Dp.	6" x .75"	3-60W Med. Base **or** 13W CFL	14.5" x 7.5"
MCKD1505TM	9" H*, 7.5" W, 5.5" Dp.	6" x .75"	1-60W Med. Base **or** 13W CFL	4.5" x 5.5" x 6"
MCKD1715TM	11.5" H, 15" W, 15" Dp.	6" x .75"	3-60W Med. Base **or** 13W CFL	13" x 15" x 6"
MCKD2819TM	15.5" H*, 19" W, 18" Dp.	6" x .75"	3-60W Med. Base **or** 13W CFL	15" x 18" x 7"

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Pearce

FINISH: Terra Bronze
GLASS: Amber and Oyster Mica

NEW!
FOR ◆ 2016

PER6323TB

PER1715TB

QUOIZEL
NATURALS
MICA

MC1691TIB

Vega

FINISH: imperial Bronze
GLASS: Oyster Mica

PRODUCT	DIMENSIONS	CANOPY	BULBS
MC1691TIB	26" H, 16" W, 16" Dp.	-	2-60W Med. Base **or** 13W CFL
PER1715TB	14" H, 15" W, 15" Dp.	6"	2-60W Med. Base or 13W CFL
PER6323TB	23" H, 15" W, 15" Dp.	-	2-60W Med. Base or 13W CFL

MCBF2822WT

MCBF1717WT

NEW!
FOR ◆ 2016

Belfair

FINISH: Western Bronze
SHADE: Silver Mica & Tempered Glass Diffuser

QUOIZEL
NATURALS
MICA

MC120T

Highland

SHADE: Soft Green Mica with Wicker Overlay

PRODUCT	DIMENSIONS	CANOPY	BULBS
MC120T	25" H, 17.5" W, 17.5" Dp.	-	2-60W Med. Base **or** 13W CFL
MCBF1717WT	9" H , 17" W, 17" Dp.	5"	4-100W Med. Base or 23W CFL
MCBF2822WT	22" H, 22" W, 22" Dp.	5"	5-100W Med. Base or 23W CFL

All chain-hung fixtures come with 8' of wire and 4' of chain.

MC2134TWT

Chandelier

FINISH: imperial Bronze
SHADE: Oyster Mica

*See matching chandelier **BDR5006IB** on page 160.*

BDR2820IB DAMP

QUOIZEL
NATURALS
MICA

NEW!
FOR ◆ 2016

Tartan

FINISH: Western Bronze
SHADE: Mica

QUOIZEL
NATURALS
AGATE STONE

AG711TVA

Whispering Wood

FINISH: Valiant Bronze
SHADE: Tiffany & Agate Stone

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE
AG711TVA	25" H, 17" W, 17" Dp.	-	2-75W Med. Base **or** 18W CFL	Contains 104 Pieces of Tiffany & Agate Stone
BDR2820IB	30" H, 20" W, 20" Dp.	5.5"	3-60W Cand. Base	
MC2134TWT	24.5" H, 16" W, 16" Dp.	-	2-60W Med. Base **or** 13W CFL	

Chain-hung fixture comes with 8' of wire and 4' of chain.

Zen

FINISH: Mystic Black
SHADE: Rattan

DAMP **ZE1717K**

DAMP **ZE1617K**

ZE2822K DAMP

Pendant converts to Semi-Flush Mount

QUOIZEL
NATURALS
RATTAN



PRODUCT	DIMENSIONS	CANOPY	BULBS
ZE1617K	6.5" H, 17" W, 17" Dp.	8.25"	3-60W Med. Base **or** 13W CFL
ZE1717K	12.5" H, 17" W, 17" Dp.	7"	3-100W Med. Base **or** 23W CFL
ZE2822K	11.5" H*, 22" W, 22" Dp.	5.25"	4-100W Med. Base **or** 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Arcadia

FINISH: imperial Bronze
SHADE: Butterscotch Onyx

NEW!
FOR ◆ 2016

QUOIZEL
NATURALS
ONYX

DAMP **AI1720IB**

AI2824IB DAMP

Zephyr

FINISH: Muted Bronze
GLASS: Frosted

INDOOR
OUTDOOR

QUOIZEL
NATURALS
SLATE

CAST
Aluminum

WET **ZP8418MD**

ZP8414MD WET

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
AI1720IB	10.5" H, 20" W, 20" Dp.	5"	-	4-100W Med. Base **or** 23W CFL
AI2824IB	22.5" H*, 24.5" W, 24.5" Dp.	5"	-	5-100W Med. Base **or** 23W CFL
ZP8414MD	14" H, 7" W, 5.5" Ext	7" x 14"	4.5"	1-50W T4 Mini Can Supplied
ZP8418MD	18" H, 9" W, 7" Ext	9" x 18"	5.5"	1-50W T4 Mini Can Supplied

All rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Aristocrat

FINISH: Palladian Bronze
SHADE: Pen Shell Mosaic

NEW!
FOR ◆ 2016

AS2824PN DAMP

DAMP AS2818PN

QUOIZEL
NATURALS
PEN SHELL

DAMP AS1716PN

PRODUCT	DIMENSIONS	CANOPY	BULBS
AS1716PN	11.5" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
AS2818PN*	21" H, 18" W, 18" Dp.	.75" x 5"	6-60W Cand. Base
AS2824PN**	25" H, 24" W, 24" Dp.	.75" x 5"	9-60W Cand. Base

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.

From the **POMEZ COLLECTION:** **TF1507VB**
Photo Courtesy of Advance Cabinetry.
www.advancecabinetry.com

Pomez COLLECTION

FINISH:
VB Vintage Bronze **BC** Burnt Cinnamon
CN Cinnamon

SHADE:
Agate Stone

TF1507VB DAMP

Enlarged for detail

TF135TBC



TF135FBC

TF6825CN

QUOIZEL
NATURALS
AGATE STONE

Pomez COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
TF135FBC	62" H, 18" W, 18" Dp.	-	3-75W Med. Base **or** 18W CFL
TF135TBC	29.5" H, 18" W, 18" Dp.	-	3-75W Med. Base **or** 18W CFL
TF1507VB	9" H*, 7" W, 7" Dp.	5.5"	1-100W Med. Base **or** 23W CFL
TF6825CN	20.5" H, 16" W, 16" Dp.	-	2-75W Med. Base **or** 18W CFL

Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

Captiva

FINISH: Vintage Bronze
SHADE: Sea Shell

NEW!
FOR ◆ 2016

SSCV6222VB

SSCV6224VB

QUOIZEL
NATURALS SEA SHELL

NEW!
FOR ◆ 2016

SSFT6221VB

the seashell COLLECTION

beautifully handcrafted from genuine seashell material

Floret

FINISH: Vintage Bronze
SHADE: Sea Shell

PRODUCT	DIMENSIONS	BULBS	SHADE
SSCV6222VB	22.5" H, 12.5" W, 12.5" Dp.	2-60W Med. Base **or** 13W CFL	Contains 216 Pieces of Sea Shell
SSCV6224VB	24" H, 16.5" W, 16.5" Dp.	2-75W Med. Base **or** 18W CFL	Contains 265 Pieces of Sea Shell
SSFT6221VB	21.5" H, 12.5" W, 12.5" Dp.	1-75W Med. Base **or** 18W CFL	Contains 156 Pieces of Sea Shell

Sanibel

FINISH: Vintage Bronze
SHADE: Sea Shell

NEW!
FOR ◆ 2016

SSSB1714VB DAMP

QUOIZEL
NATURALS
SEA SHELL

SSSB6223VB

NEW!
FOR ◆ 2016

Flower Field

FINISH: Vintage Bronze
SHADE: Jade

JD2077TVB

QUOIZEL
NATURALS
JADE

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE
JD2077TVB	25" H, 15.5" W, 15.5" Dp.	-	2-75W Med. Base **or** 18W CFL	Contains 264 Pieces of Jade
SSSB1714VB	15" H, 14" W, 14" Dp.	5"	2-60W Med. Base **or** 13W CFL	Contains 252 Pieces of Sea Shell
SSSB6223VB	23" H, 16" W, 16" Dp.	-	2-60W Med. Base **or** 13W CFL	Contains 181 Pieces of Sea Shell



Kendra Collection

Finish: Mottled Silver **Shade:** Oyster Mica

*For larger images and all product specifications, please see **The Kendra Collection** as it is represented in the Collections Section on pages 64-67.*

KD5015MM

KD5009MM

KD5005MM

KD2824MM

KD2816MM

KD1507MM

KD1716MM

QUOIZEL NATURALS MICA

KD8701MM



Kyle COLLECTION

IB **Finish:** Imperial Bronze **Shade:** Butterscotch Onyx
IN **Finish:** Iron Gate **Shade:** White Onyx

*For larger images and all product specifications, please see **The Kyle Collection** as it is represented in the Collections Section on pages 68-73.*

KY5016IB

KY5009IB/IN

KY5006IN/IB

KY5506IB

KY1404IB

KY8701IN/IB

KY540IB/IN

KY433IB

KY5106IB

KY6328IB

KY5503IB

KY5103IN/IB

KY2822IB

KY1507IN/IB

KY1508IB/IN

KY8801IB/IN

KY1716IB

QUOIZEL NATURALS ONYX

MontereyMosaicCOLLeCTiOn

Finish: Malaga **Shade:** Pen Shell Mosaic

*For larger images and all product specifications, please see **The Monterey Mosaic Collection** as it is represented in the Collections Section on pages 81-86.*

MY5005ML

MY5103ML

MY2824ML

MY2816ML

MY1723ML

MY1718ML

MY1613ML

MY1618ML

MY1404ML

MY8801ML

MY1506ML

QUOIZEL
NATURALS
PEN SHELL

MY430242ML

MY430241ML

QUOIZEL NATURALS

Please see referenced page numbers for larger images and full descriptions of these products.

QUOIZEL

NATURALS

Please see referenced page numbers for larger images and full descriptions of these products.

Baron

BRO5203MK

See page 110

Baron

BRO1715MK

See page 110

Castile

CS5012RK

See page 111

Castile

CS5006RK

See page 111

Castile

CS1718RK

See page 111

Tavern

TVN232DK

See page 120

Tavern

TVN5005DK

See page 120

Tavern

TVN1717DK

See page 120

Odell

ODL5009IB

See page 124

Odell
ODL5005IB
See page 125

Odell
ODL5303IB
See page 125

Odell
ODL2820IB
See page 125

Odell
ODL5206IB
See page 125

Auburn
ABN5024RK
See page 142

Auburn
ABN5012RK
See page 144

Auburn
ABN5006RK
See page 144

Belhaven
BHN5009VG
See page 157

Belhaven
BHN5006VG
See page 157

Belhaven
BHN5303VG
See page 157

Bandelier
BDR5006IB
See page 160

Wyndmoor
WDM5005WT
See page 160

QUOIZEL

NATURALS

Please see referenced page numbers for larger images and full descriptions of these products.

Holbrook
HK5008TC
See page 166

Holbrook
HK5005TC
See page 166

Planter
QF1840RK
See page 166

Kayden
KDN5004BN
See page 169

Pembroke
PB5008TK
See page 170

Pembroke
PB5004TK
See page 170

Anchor
ANR5010IB
See page 171

Anchor
ANR5006IB
See page 171

Kayden
KDN1510BN
See page 280

From the **DELUXE COLLECTION: DX348C** (p.261)
Photo Courtesy of Natalie Howe Design.

Brook Hall

FINISH: Western Bronze

See matching Brook Hall styles starting on p. 42

NEW!
FOR ◆ 2016

BKH838WT DAMP

Alexandria

FINISH: Palladian Bronze

AX434PN DAMP

See matching Alexandria styles on p. 104

DANGLING GLASS ACCENTS

Laguna

FINISH: Renaissance Copper
SHADE: Oyster Mica & Mosaic t ile

MCLG337RC DAMP

See matching Laguna styles starting on p. 228

QUOIZEL NATURALS MICA

PRODUCT	DIMENSIONS	CANOPY	BULBS
AX434PN†	8" H*, 15.5" W, 33.5" Dp.	4.5"	4-100W Med. Base **or** 23W CFL
BKH838WT	15.5" H, 38" W, 12" Dp.	9" x 4.75"	8-60W Cand. Base
MCLG337RC††	21" H*, 37" W, 16" Dp.	7.5" x 4.5"	3-100W Med. Base **or** 23W CFL

Chain-hung fixture comes with 8' of wire and 4' of chain. †Rod-hung fixture comes with 8' of wire.
††Rod-hung fixture comes with 12' of wire. *Comes with (4) 6" and (4) 12" Rods.

ADS639DC

Adonis

FINISH: d ark Cherry
GLASS: Opal Etched and Clear Water

See matching Adonis styles starting on p. 38

Emery

FINISH: **BN** Brushed n ickel
IS imperial s ilver
PN Palladian Bronze

SHADE: Metal

ER353BN

See matching Emery styles starting on p. 61

***ER353** is available in THREE finishes!*

PRODUCT	DIMENSIONS	CANOPY	BULBS
ADS639DC††	19" H*, 39" W, 19.5" Dp.	8" x 4.5"	6-60W Cand. Base
ER353BN/IS/PN†	23.5" H*, 52.5" W, 13" Dp.	9" x 4.5"	3-100W Med. Base **or** 23W CFL

†Rod-hung fixture comes with 8' of wire. ††Fixture comes with 10' of wire. *Comes with (4) 6" and (4) 12" Rods.

Eastvale

FINISH: Palladian Bronze
SHADE: Metal with Clear Ribbed g lass d iffuser

See matching Eastvale styles on p. 105

DAMP **EVE240PN**

CLEAR RIBBED DIFFUSER

Tavern

FINISH: d arkest Bronze

See matching Tavern styles on p. 120

DAMP **TVN232DK**

QUOIZEL NATURALS WOOD

NewHarbor

FINISH: Western Bronze

NHR538WT DAMP

See matching New Harbor styles on p. 133

PRODUCT	DIMENSIONS	CANOPY	BULBS
EVE240PN	29" H*, 40" W, 14.5" Dp.	6"	2-100W Med. Base **or** 23W CFL
NHR538WT	9.5" H**, 38" W, 12" Dp.	9" x 4.75" x .75"	5-60W Vintage Bulbs Supplied†
TVN232DK	10.5" H**, 32" W, 12" Dp.	10.5" x 4.5"	6-60W Vintage Bulbs Supplied†

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
Comes with (4) 6" and (4) 12" Rods. †Max Wattage: 100W Med. Base **or 23W CFL.

From the **CAROLYN KINDER MARISOL COLLECTION:**
CKMS442TM

Confetti

FINISH: OS Old silver **RK** Rustic Black NEW!
SHADE: Outer: Metal Confetti
inner: Off-White linen

See matching Confetti styles starting on page 208

NEW!
FOR ◆ 2016

DAMP **CKCF339RK**

CKCF339OS DAMP

Carolyn Kinder INTERNATIONAL

DAMP **CKMS442TM**

Marisol

FINISH: Teco Marrone
SHADE: Beige hardback linen

See matching Marisol styles on page 213

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE
CKCF339OS/RK†	9" H*, 39.5" W, 8" Dp.	.75" x 4.5"	3-100W Med. Base **or** 23W CFL	-
CKMS442TM††	32.5" H, 42" W, 11" Dp.	5" x 9.75"	5-100W Med. Base **or** 23W CFL	8.5" x 39.5" x 8"

†Rod-hung fixtures come with 8' of wire. *Comes with (6) 6" and (6) 12" Rods. ††Chain-hung fixture comes with 8' of wire and 4' of chain.

DH348AN

Duchess

FINISH: AN a ntique n ickel **PN** Palladian Bronze
SHADE: AN g rey Marble **PN** Champagne Marble

DH348PN

See matching Duchess styles starting on p. 52

La Parra

FINISH: imperial Bronze
SHADE: Candella scavo

See matching La Parra styles starting on p. 74

LP639IB

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH348AN/PN	27" H, 48" W, 14" Dp.	6.5"	3-100W Med. Base **or** 23W CFL
LP639IB	46" H, 38" W, 19" Dp.	7" x 4.5"	6-100W Med. Base **or** 23W CFL

Chain-hung fixture comes with 8' of wire and 4' of chain.

QUOIZEL
NATURALS
ONYX

KY540IN DAMP

Kyle

FINISH: **IB** imperial Bronze
IN iron g ate

SHADE: **IB** Butterscotch Onyx
IN White Onyx

***KY540** is also available in Imperial Bronze*



See matching Kyle styles in the starting on on page 68



KY433IB DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
KY433IB	18.5" H, 33" W, 4.5" Dp.	8" x 4.5"	4-100W Med. Base **or** 23W CFL
KY540IB/IN	23" H, 40" W, 5.5" Dp.	11.75" x 4.75"	5-100W Med. Base **or** 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

DX348C

Deluxe

FINISH: Polished Chrome
SHADE: Cream l inen h ardback

See matching Deluxe styles on pages 290 and 349

CRYSTAL ACCENTS

TY628AN

Taylor

FINISH: a ntique n ickel
GLASS: Opal Etched

See matching Taylor styles starting on p. 87

Remi

FINISH: Polished Chrome
SHADE: White Fabric

See matching Remi styles on p. 123

REM345C

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
DX348C†	33" H, 48" W, 12" Dp.	8"	3-150W Med. Base **or** 40W CFL	10" x 48" x 12"
REM345C††	10" H, 44.5" W, 5.5" Dp.	18" x 4.5"	3-75W Med. Base **or** 18W CFL	6" x 10.5" x 5.5"
TY628AN**	16.5" H*, 28" W, 16" Dp.	9" x 4.75" x 0.875"	6-100W Med. Base **or** 23W CFL	-

*Comes with (4) 6" and (4) 12" Rods. **Rod-hung fixture comes with 8' of wire.
†Chain-hung fixture comes with 8' of wire and 4' of chain. ††Cable-hung fixture comes with 12' of wire.

Asheville

FINISH: Valiant Bronze

See matching Asheville styles starting on page 470

DAMP **TFAS344VA**

Belle Fleur

FINISH: Vintage Bronze

See matching Belle Fleur styles starting on page 483

TFBF348VB DAMP

Inglenook

FINISH: Valiant Bronze

See matching Inglenook styles starting on page 464

DAMP **TFIK348VA**

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TFAS344VA	29" H, 44" W, 19" Dp.	10" x 4.5" x 1"	3-100W Med. Base **or** 23W CFL	Contains 316 Pieces of Tiffany Glass
TFBF348VB	18" H, 48" W, 16" Dp.	8" x 4.5"	3-100W Med. Base **or** 23W CFL	Contains 884 Pieces of Tiffany Glass
TFIK348VA	17.5" H, 47.5" W, 16" Dp.	8" x 4.5"	3-100W Med. Base **or** 23W CFL	Contains 496 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

MOROCCO PENDANT:
QF2046C (p. 270)

Orion COLLECTION

FINISH:
BN Brushed Nickel **WT** Western Bronze

GLASS: Clear Accents



NEW!
FOR ◆ 2016

ON2824BN DAMP

ON2824WT DAMP

ON2818WT DAMP

Pendants convert to Semi-Flush Mounts

ON2818BN DAMP

Orion COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ON2818BN/WT	19.5" H*, 18" W, 18" Dp.	5.5"	4-60W Cand. Base
ON2824BN/WT	25.5" H*, 24" W, 24" Dp.	5.5"	6-60W Cand. Base

All rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Jarvis

FINISH: o ld Silver
SHADE: o ff White l inen Hardback Fabric

JV2820OS

SAND BLASTED DIFFUSER

NEW! FOR ◆ 2016

Pendant convert to Semi-Flush Mount

JV2816OS

Amelia

FINISH: o ld Bronze
GLASS: Etched Painted White inside

NEW! FOR ◆ 2016

*See matching chandelier **AML5005OZ** on page 162.*

AML2821OZ

GLASS ACCENTS

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
AML2821OZ††	24.5" H, 21" W, 21" Dp.	1.5" x 5.75"	3-100W Med. Base **or** 23W CFL	-
JV2816OS†	10" H*, 16" W, 16" Dp.	5.5"	3-100W Med. Base **or** 23W CFL	8" x 14" x 14"
JV2820OS†	10" H*, 20" W, 20" Dp.	5.5"	3-100W Med. Base **or** 23W CFL	8" x 17" x 17"

*Comes with (2) 6" and (2) 12" Rods. †Rod-hung fixtures come with 8' of wire. ††Chain-hung fixture comes with 8' of wire and 4' of chain.

From the **PORTLAND COLLECTION:**
PTD2826WT
Photo courtesy of LDK Homes

Pendant converts to Semi-Flush Mount

Portland

FINISH: **BN** Brushed Nickel
WT Western Bronze

SHADE: **BN** Clear Organza with Light Grey Trim
WT Light Amber Organza with Bronze Trim

PTD2826BN DAMP

Pendant converts to Semi-Flush Mount

PTD2820WT DAMP

BWL2822CC DAMP

BWL2816CC DAMP

STUDDED FAUX BRASS ACCENTS

Brown Lattice

FINISH: Copper Canyon
SHADE: Outer: Metal with Studded Faux Brass Accents
Inner: Tan Fabric Hardback

See matching Brown Lattice styles on page 280 and 288.

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
BWL2816CC	10" H*, 16" W, 16" Dp.	5.5"	3-100W Med. Base **or** 23W CFL	Outer: 16" x 10", Inner: 15" x 9.5"
BWL2822CC	10" H*, 22" W, 22" Dp.	5.5"	4-100W Med. Base **or** 23W CFL	Outer: 22" x 10", Inner: 21" x 9.5"
PTD2820BN/WT	16.5" H*, 20" W, 20" Dp.	5"	4-60W Cand. Base	20" x 6"
PTD2826BN/WT	24" H*, 28" W, 28" Dp.	5"	8-60W Cand. Base	28" x 8"

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

See matching flush mount ***BND1613BA*** *on page 307.*

Capri

FINISH: imperial Bronze
SHADE: Beige l inen with Brown Trim

See matching chandelier ***CP5006IB*** *on page 160.*

DAMP **CP2820IB**

DAMP **BND1818BA**

Bound

FINISH: Royal Ebony

Pendant converts to Semi-Flush Mount

DAMP **RLY1815IB**

Pendant converts to Semi-Flush Mount

Railway

FINISH: imperial Bronze

See matching mini-pendant ***RLY1512IB*** *on page 283.*

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
BND1818BA	7.5" H*, 18" W, 18" Dp.	5.5" x .75"	4-40W T8 Vintage Bulbs Supplied**	-
CP2820IB	14.5" H*, 20" W, 20" Dp.	5"	4-60W Cand. Base	16" x 16" x 7"
RLY1815IB	11" H*, 15.5" W, 15.5" Dp.	6" x .75"	1-100W Med. Base **or** 23W CFL	-

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 60W Cand. Base.

JLE2812IS DAMP

Jolene

FINISH: Imperial Silver

*See matching semi-flush mount **JLE1709IS** on page 296.*

JLE2809IS DAMP

MIR2818VG DAMP

Mirage

FINISH: Vintage Gold

See matching Mirage styles on page 296.

PRODUCT	DIMENSIONS	CANOPY	BULBS
JLE2809IS	19" H , 9" W, 9" Dp.	5"	2-60W Cand. Base
JLE2812IS	22" H, 12" W, 12" Dp.	5"	3-60W Cand. Base
MIR2818VG	21.5" H, 18.5" W, 18.5" Dp.	6" x 0.75"	4-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

CDY2814BN

Cody

FINISH: Brushed Nickel

See matching Cody styles on page 280 & 297.

QF2046C

Morocco

FINISH: Polished Chrome
GLASS: Clear Hand Blown

*See matching mini pendant **QF2047C** on page 279.*

HAND BLOWN GLASS

NEW!
FOR ◆ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
CDY2814BN††	10.5" H*, 14.5" W, 14.5" Dp.	5"	2-100W Med. Base **or** 23W CFL
QF2046C†	21.5" H*, 16" W, 16" Dp.	.75 x 5.75"	1-60W Vintage Bulb Supplied**

†Cable-hung fixtures come with 8' of wire. ††Rod-hung fixtures come with 12' of wire.
*Comes with (2) 6" and (2) 12" Rods. **Max. Wattage: 100W Med. Base **or** 23W CFL.

CRA2826MC

Cloverdale

FINISH: Mottled Cocoa
SHADE: Khaki Fabric

See matching semi-flush ***CRA1717MC*** *on page 290.*

CRA2822MC

Pendant converts to Semi-Flush Mount

Pendant converts to Semi-Flush Mount

LongBeach

FINISH: Western Bronze

LBH2820WT

Pendant converts to Semi-Flush Mount



PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
CRA2822MC	12" H*, 22" W, 22" Dp.	5.5"	4-100W Med. Base **or** 23W CFL	22" x 10.5"
CRA2826MC	9.5" H*, 26" W, 26" Dp.	6.5"	4-100W Med. Base **or** 23W CFL	26" x 8"
LBH2820WT	10.5" H*, 20" W, 20" Dp.	6" x 1"	3-60W Vintage Bulb (Supplied)**	-

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 100W Med Base **or** 23W CFL.

Pendants

Please see referenced page numbers for larger images and full descriptions of these products.

Adonis

ADS2818DC

See page 39

Baroness

BNS2818WT

See page 41

Buchanan

BCN2820WT

See page 45

Downtown

DW1824C

See page 51

Downtown

DW2817C

See page 51

Duchess

DH2820AN/PN

See page 54

Dury

RDY2821PN/CS

See page 60

Dury

RDY2823CS/PN

See page 60

Emery

ER1814BN/IS/PN

See page 62

Kendra

KD2816MM

See page 67

Kendra

KD2824MM

See page 67

Kyle

KY2822IB

See page 72

Monterey Mosaic

MY2816ML

See page 84

Monterey Mosaic

MY2824ML

See page 84

Trilogy

TRG1816OZ

See page 94



Adams

ADA2820LN

See page 103

Alexandria

AX2820PN

See page 104

Alexandria

AX2826PN

See page 104

Eastvale

EVE2815PN

See page 105

Milbank

MBK2820VG

See page 113

Grant

GRT2814BN/IS/PN

See page 115

Metropolis

MTP2820AN

See page 117

Metropolis

MTP2823AN

See page 117



Palmer

PLR2820PN

See page 122

Pendants

Please see referenced page numbers for larger images and full descriptions of these products.

Odell

ODL2820IB

See page 125

Wilder

WLR2820MB

See page 135

Pl ATiNUM Co l l ECTio N

Bordeaux

BRX2818C

See page 174

Pl ATiNUM Co l l ECTio N

Galaxy

PCGX1817C

See page 178



Pl ATiNUM Co l l ECTio N

Galaxy

PCGX1826C

See page 178

Pl ATiNUM Co l l ECTio N

Arena

PCAN2814C

See page 180

Pl ATiNUM Co l l ECTio N

Crystal Leaf

PCCF2824C

See page 180

Pl ATiNUM Co l l ECTio N

Mercury

PCMY2818C

See page 181

Pl ATiNUM Co l l ECTio N

Vision

PCVN2820C

See page 182

Pl ATiNUM Co l l ECTio N

Janelle

PCJL2820C

See page 183

Pl ATiNUM Co l l ECTio N

Superior

PCSP2823C

See page 184

Pl ATiNUM Co l l ECTio N

Valla

VLA2820C

See page 185

Pl ATiNUM Co l l ECTio N
Ribbons
RBN2831CRC
See page 186

Pl ATiNUM Co l l ECTio N
Ribbons
RBN2823CRC
See page 186

Pl ATiNUM Co l l ECTio N
Ribbons
RBN2817CRC
See page 186

Pl ATiNUM Co l l ECTio N
Ribbons
RBN2831C/MN/SG/W/WT
See page 188



Pl ATiNUM Co l l ECTio N
Ribbons
RBN2823C/MN/SG/W/WT
See page 189



Pl ATiNUM Co l l ECTio N
Ribbons
RBN2817C/MN/SG/W/WT
See page 189

Pl ATiNUM Co l l ECTio N
Abode
PCAE2820C
See page 190

Pl ATiNUM Co l l ECTio N
Encompass
PCEC1820MN
See page 192

CARo l YN KiNDER
Confetti
CKCF2822OS/RK
See page 208

CARo l YN KiNDER
Confetti
CKCF2825OS/RK
See page 208

CARo l YN KiNDER
Confetti
CKCF2816OS/RK
See page 209

CARo l YN KiNDER
Metro
CKMO2820BN
See page 210

From the **LAGUNA COLLECTION: MC8420CRC** (p.228)
Photo Courtesy of Devane Designs

CARoLYN KiNDER
Marisol
CKMS2822TM
See page 213



UPTOWN
COLLECTION
Fulton
UPFT1820IS
See page 224

UPTOWN
COLLECTION
Penn Station
UPPS2813BN/WT
See page 225

Laguna

MC8420CRC

See page 228

Laguna

MC842CRC

See page 228

Morrow

MC1910MM

See page 235



Kingsford

MCKD2819TM

See page 235

Belfair

MCBF2822WT

See page 237

Bandelier

BDR2820IB

See page 238

Zen

ZE2822K

See page 239

Arcadia

AI2824IB

See page 240

Aristocrat

AS2818PN

See page 241

Aristocrat

AS2824PN

See page 241

*Please see the **Quoizel Tiffany Collection** on **page 459** for many attractive art glass pendant lighting solutions.*

From the **TIFFANY HYACINTH COLLECTION:**
TF1536VB (p.487)
Photo courtesy of Enmark Construction Ltd.

Morocco

FINISH: Polished Chrome
GLASS: Clear Hand Blown



*See matching pendant **QF2046C** on page 270.*

NEW!
FOR ◆ 2016

HAND BLOWN GLASS

DAMP **QF2047C**

DAMP **QPP2049WT**

DAMP **QPP2049BN**

NEW!
FOR ◆ 2016

Garrison

FINISH: **BN** Brushed Nickel
WT Western Bronze
GLASS: o pal Etched

See matching Garrison bath styles on page 351.

PRODUCT	DIMENSIONS	CANOPY	BULBS
QF2047C†	13.5" H, 10" W, 10" Dp.	.75 x 5.75"	1-60W Vintage Bulb Supplied**
QPP2049BN/WT††	7.5" H*, 7.5" W, 7.5" Dp.	5"	1-100W Med. Base or 23W CFL

†Cable-hung fixtures come with 8' of wire. ††Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max. Wattage: 100W Med. Base **or** 23W CFL.

Brown Lattice

FINISH: Copper Canyon
SHADE: outer: Metal with Faux Brass Studded Accents
inner: Tan Fabric Hardback

See matching Brown Lattice styles on pages 267 and 288.

BWL1508CC DAMP

CDY1508BN DAMP

Cody

FINISH: Brushed Nickel

See matching Cody styles on pages 270 & 297.

Ferndale

FINISH: Western Bronze
GLASS: outer: Clear Seedy
inner: Tiffany Glass

FE1506WT DAMP

DAMP **KDN1510BN**

QUOIZEL NATURALS WOOD

Kayden

FINISH: Brushed Nickel
GLASS: Clear Seedy

*See matching chandelier **KDN5004BN** on page 169.*

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
BWL1508CC†	9" H*, 8" W, 8" Dp.	5.5"	1-100W Med. Base **or** 23W CFL	Outer: 8" x 9", Inner: 7.5" x 8.75"
CDY1508BN**	9" H*, 8" W, 8" Dp.	5"	1-100W Med. Base **or** 23W CFL	
FE1506WT**	12.5" H*, 6" W, 6" Dp.	6"	1-100W Med. Base **or** 23W CFL	-
KDN1510BN**	10.5" H*, 10" W, 10" Dp.	5"	1-60W Cand. Base	

*Comes with (2) 6" and (2) 12" Rods. **Rod-hung fixtures come with 8' of wire. †Fixture comes with 10' of wire.

INDOOR OUTDOOR

Steadman

FINISH: imperial Bronze
GLASS: Clear Seedy

See matching Steadman styles on page 436-437.

SDN1506IB DAMP

MRE1506WT DAMP

See matching Marine styles on page 426-427.

Ridley

FINISH: Western Bronze
GLASS: Clear

VINTAGE STYLE
bulb included



Marine

INDOOR OUTDOOR

FINISH: Western Bronze

CAST *Aluminum*

QPP1401WT DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
MRE1506WT††	12" H*, 6" W, 6" Dp.	6"	1-60W Vintage Bulb Supplied**
QPP1401WT††	11" H*, 11.5" W, 11.5" Dp.	6"	1-60W Vintage Bulb Supplied**
SDN1506IB†	12" H*, 5.5" W, 5.5" Dp.	6"	1-60W Vintage Bulb Supplied**

*Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 100W Med. Base **or** 23W CFL. †Rod-hung fixture comes with 8' of wire. ††Fixture comes with 10' of wire.

Dublin

FINISH: Brushed Nickel
GLASS: Clear Pressed

See matching Dublin styles on page 345.

DAMP **DBN1506BN**

DAMP **QPP2048BN**

Valentina

FINISH: Brushed Nickel
SHADE: o uter: Clear Glass
inner: Metal

QPP2050BN DAMP

Antero

FINISH: Brushed Nickel
GLASS: Clear Seedy

NEW!
FOR ◆ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
DBN1506BN	7.5" H*, 6.5" W, 6.5" Dp.	5"	1-100W Med. Base **or** 23W CFL
QPP2048BN	13" H*, 6" W, 6" Dp.	1" x 5"	1-100W Med. Base **or** 23W CFL
QPP2050BN	8" H*, 4.5" W, 4.5" Dp.	4.75"	1-60W Clear G9 Xenon Supplied

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Railway

FINISH: imperial Bronze
SHADE: Metal

*See matching pendant **RLY1815IB** on page 268.*

DAMP **RLY1512IB**

Mini-Pendant converts to Semi-Flush Mount



Highgate

FINISH: imperial Silver
GLASS: Clear

QPP2051IS DAMP

NEW!
FOR ◆ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
QPP2051IS	13.5" H*, 9.5" W, 9.5" Dp.	6"	1-60W Vintage Bulb Supplied**
RLY1512IB	8" H*, 12" W, 12" Dp.	6" x .75"	1-100W Med. Base **or** 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 100W Med. Base **or** 23W CFL.

Mini Pendants

Please see referenced page numbers for larger images and full descriptions of these products.

Adonis

ADS1504DC

See page 39

Baroness

BNS1505WT

See page 40

Downtown

DW1506C/D

See page 51

Duchess

DH1506AN/PN

See page 56

Dury

RDY1506CS

See page 60

Emery

ER1508BN/IS/PN

See page 62

Kendra

KD1507MM

See page 67

Kyle

KY1507IB/IN

See page 73

Kyle

KY1508IB/IN

See page 73

La Parra

LP1505IB

See page 76

Monterey Mosaic

MY1506ML

See page 86

Trilogy

TRG1508OZ

See page 94

Eastvale

EVE1508PN

See page 105

Grant

GRT1508BN/IS/PN

See page 115

Metropolis

MTP1510AN

See page 117

New England

NA1514BN

See page 119

New England

NA1510BN

See page 119

Sophia

SPH1508PN/BN

See page 132

Wilder

WLR1506MB

See page 135

Union Station

UST1505WT

See page 140

Pl ATiNUM Co l l ECTio N

Treasure

PCTS1503C

See page 181

Pl ATiNUM Co l l ECTio N

Ribbons

RBN1512CRC

See page 187

Pl ATiNUM Co l l ECTio N

Ribbons

RBN1512C/MN/SG/W/WT

See page 189

CARo lYN KiNDER

Confetti

CKCF1508OS/RK

See page 209

Mini Pendants

Please see referenced page numbers for larger images and full descriptions of these products.

CARoLYN KiNDER

Gaston

CKGN1509MZ

See page 215

CARoLYN KiNDER

Kendrick

CKKD1509WT

See page 215

CARoLYN KiNDER

Nikos

CKNK1509BV

See page 215

CARoLYN KiNDER

Sonia

CKSN1507AR

See page 215

UPTOWN COLLECTION

Penn Station

UPPS1510BN/WT

See page 225

Laguna

MC842PRC

See page 232

Kingsford

MCKD1505TM

See page 235

Pomez

TF1507VB

See page 243

*Please see the **Quoizel Tiffany Collection** on **page 459** for many attractive art glass mini pendant lighting solutions.*

From the
OZARK COLLECTION:
OZ1616IN (p.306)

QUOIZEL

SEMI-FLUSH & FLUSH MOUNTS

Brown Lattice

FINISH: Copper Canyon
SHADE: Outer: Metal Shade with Faux Studded Brass Accents
Inner: Tan Fabric Hardback

See matching Brown Lattice style on page 267 and 280.

DAMP **BWL1717CC**

FAUX BRASS ACCENTS

Burgess

FINISH: Rustic Black
GLASS: Mercury

NEW!
FOR ◆ 2016

BGS1715RK DAMP

*See matching chandelier **BGS5203RK** on page 170.*

DAMP **FTR1713IB**

Frontier

FINISH: Imperial Bronze

*See matching chandelier **FTR5204IB** on page 161.*

PRODUCT	DIMENSIONS	CANOPY	BULBS
BGS1715RK	15.5" H, 15" W, 15" Dp.	5"	3-60W Cand. Base
BWL1717CC	11" H, 17" W, 17" Dp.	5.5"	3-100W Med. Base **or** 23W CFL
FTR1713IB	13" H, 13" W, 13" Dp.	0.75"	3-60W Cand. Base

QF1213SHO DAMP

QF1213SBN DAMP

Norwood

FINISH: **BN** Brushed Nickel
HO Harbor Bronze
GLASS: Opal Etched

CLT1714BN DAMP

Celestial

FINISH: Brushed Nickel
GLASS: Opal Etched

See matching chandelier ***CLT5004BN*** *on page 162.*

PRODUCT	DIMENSIONS	CANOPY	BULBS
CLT1714BN	15" H, 14" W, 14" Dp.	5"	4-100W Med. Base **or** 23W CFL
QF1213SBN/SHO	11" H, 19" W, 19" Dp.	6" Sq.	4-100W Med. Base **or** 23W CFL

Waverly

FINISH: Brushed Nickel
SHADE: White Linen Fabric

WV1716BN

See matching Deluxe styles on pages 261 and 349

Deluxe

FINISH: Polished Chrome
SHADE: Cream Linen Hardback

DX1718C

CRYSTAL FINIAL

FROSTED WHITE DIFFUSER

CRA1717MC

Cloverdale

FINISH: Mottled Cocoa
SHADE: Khaki Fabric

See matching Cloverdale styles on page 271.

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
CRA1717MC	12.5" H, 17" W, 17" Dp.	6.5"	3-100W Med. Base **or** 23W CFL	-
DX1718C	16.5" H, 18" W, 18" Dp.	8"	3-60W Med. Base **or** 13W CFL	7" x 15.5" x 17.5"
WV1716BN	11.5" H, 16" W, 16" Dp.	6"	3-100W Med. Base **or** 23W CFL	4" x 14" x 16"

From the
DELUXE COLLECTION:
DX1718C
Photo Courtesy of Studio M. Interiors

SLR1716AN

Sailor

FINISH: **AN** Antique Nickel
WT Western Bronze
GLASS: Etched

SLR1720WT

NEW!
FOR ◆ 2016

Calvary

FINISH: Western Bronze
SHADE: Light Beige Fabric Hardback

QF1715WT

ETCHED GLASS DIFFUSER

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
QF1715WT	10.5" H, 17.5" W, 17.5" Dp.	6"	3-100W Med. Base **or** 23W CFL	15" x 5"
SLR1716AN/WT	9.5" H, 16" W, 16" Dp.	5"	4-100W Med. Base **or** 23W CFL	
SLR1720AN/WT	9.5" H, 20" W, 20" Dp.	6"	5-100W Med. Base **or** 23W CFL	

Ashland

FINISH: Western Bronze
GLASS: Etched Painted White Inside

DAMP **QF1202SWT**

DAMP **QF1201SWT**

OZ1713IN DAMP

OZ1716PN DAMP

Ozark

FINISH: **IN** Iron Gate **PN** Palladian Bronze
GLASS: Etched Painted White Inside

See matching Ozark flush mounts on page 306.

PRODUCT	DIMENSIONS	CANOPY	BULBS
OZ1713IN/PN	9.5" H, 13" W, 13" Dp.	5"	2-100W Med. Base **or** 23W CFL
OZ1716IN/PN	12" H, 16.5" W, 16.5" Dp.	5"	3-100W Med. Base **or** 23W CFL
QF1201SWT	12" H, 25" W, 25" Dp.	6"	4-100W Med. Base **or** 23W CFL
QF1202SWT	11" H, 20" W, 20" Dp.	6"	3-100W Med. Base **or** 23W CFL

Griffin

FINISH: **AN** Antique Nickel
PN Palladian Bronze
GLASS: Etched Painted White Inside

See matching Griffin flush mounts on page 305.

GF1721AN DAMP

Enlarged for detail

GF1717AN DAMP

DAMP **GF1721PN**

DAMP **GF1717PN**

PRODUCT	DIMENSIONS	CANOPY	BULBS
GF1717AN/PN	12" H, 17" W, 17" Dp.	5.75"	3-100W Med. Base **or** 23W CFL
GF1721AN/PN	14" H, 21" W, 21" Dp.	5.75"	4-100W Med. Base **or** 23W CFL

From the **GRIFFIN COLLECTION:**
GF1717PN

Jolene

FINISH: Imperial Silver

JLE1709IS DAMP

See matching Jolene styles on page 269.

CRYSTAL STRANDS

DAMP **MJY1615VG**

Majesty

FINISH: Vintage Gold

*See matching chandelier **MJY5304VG** on page 159.*

Mirage

FINISH: Vintage Gold

*See matching pendant **MIR2818VG** on page 269.*

MIR1715VG DAMP

DAMP **MIR1718VG**

PRODUCT	DIMENSIONS	CANOPY	BULBS
JLE1709IS	13.5" H, 9.5" W, 9.5" Dp.	4.5"	2-60W Cand. Base
MIR1715VG	11.5" H, 15" W, 15" Dp.	6"	3-100W Med. Base **or** 23W CFL
MIR1718VG	11.5" H, 18.5" W, 18.5" Dp.	6"	4-100W Med. Base **or** 23W CFL
MJY1615VG	14" H, 15.5" W, 15.5" Dp.	1.25" x 5"	4-60W Cand. Base

Cody

FINISH: Brushed Nickel

See matching Cody styles on pages 270 and 280.

CDY1714BN DAMP

Warren

FINISH: Brushed Nickel
GLASS: Opal Etched

DAMP **QF1678BN**

DAMP **QF1834BN**

Belcourt

FINISH: **BN** Brushed Nickel
WT Western Bronze
GLASS: Etched Painted White Inside

DAMP **QF1831BN**

Castle

FINISH: Brushed Nickel
GLASS: Etched Painted White Inside

PRODUCT	DIMENSIONS	CANOPY	BULBS
CDY1714BN	12" H, 14.5" W, 14.5" Dp.	5"	2-100W Med. Base **or** 23W CFL
QF1678BN	10" H, 13.5" W, 13.5" Dp.	6.5"	1-100W Med. Base **or** 23W CFL
QF1831BN	10" H, 17" W, 17" Dp.	6"	4-100W Med. Base **or** 23W CFL
QF1834BN/WT	11" H, 18" W, 18" Dp.	5"	3-100W Med. Base **or** 23W CFL

Semi-Flush Mounts

Please see referenced page numbers for larger images and full descriptions of these products.

Baroness

BNS1715WT

See page 41

Brook Hall

BKH1714WT

See page 42

Buchanan

BCN1716WT

See page 45

Downtown

DW1717C/D

See page 51

Duchess

DH1718AN/PN

See page 56

Dury

RDY1714CS/PN

See page 60

Kendra

KD1716MM

See page 67

Kyle

KY1716IB

See page 72

Monterey Mosaic

MY1718ML

See page 85

Monterey Mosaic

MY1723ML

See page 85

Taylor

TY1716AN

See page 90

Taylor

TY1721AN

See page 90

Trilogy

TRG1712OZ

See page 95

Trilogy

TRG1716OZ

See page 95

Whitney

WHI1716IS

See page 100

Baron

BRO1715MK

See page 110

Castile

CS1718RK

See page 111

Milbank

MBK1716VG

See page 113

Metropolis

MTP1718AN

See page 117

Tavern

TVN1717DK

See page 120

Palmer

PLR1716PN

See page 122

New Harbor

NHR1718WT

See page 133

Wilder

WLR1716MB

See page 135

Union Station

UST1716WT

See page 140

Semi-Flush Mounts

Please see referenced page numbers for larger images and full descriptions of these products.

PLATINUM COLLECTION
Alexa
PCAX1714C
See page 179

PLATINUM COLLECTION
Crowne
PCCR1717CC
See page 180

PLATINUM COLLECTION
Shimmer
PCSR1716C
See page 181

PLATINUM COLLECTION
Vision
PCVN1716C
See page 182

PLATINUM COLLECTION
Superior
PCSP1718C
See page 184

PLATINUM COLLECTION
Array
PCAY1722C
See page 190

PLATINUM COLLECTION
Abode
PCAE1715C
See page 190

CAROLYN KINDER
Confetti
CKCF1717OS/RK
See page 209

CAROLYN KINDER
Confetti
CKCF1720OS
See page 209

CAROLYN KINDER
Confetti
CKCF1714OS
See page 209

CAROLYN KINDER
Metro
CKMO1716BN
See page 210

CAROLYN KINDER
Marisol
CKMS1716TM
See page 213

UPTOWN COLLECTION

Theater Row

UPTR1716WT

See page 218

UPTOWN COLLECTION

Penn Station

UPPS1713BN/WT

See page 225

Laguna

MC842SRC

See page 228

Kingsford

MCKD1715TM

See page 235

Pearce

PER1715TB

See page 236

Belfair

MCBF1717WT

See page 237

Zen

ZE1717K

See page 239

Arcadia

AI1720IB

See page 240

Aristocrat

AS1716PN

See page 241

Sanibel

SSSB1714VB

See page 245

*Please see the **Quoizel Tiffany Collection** on **page 459** for many attractive art glass semi-flush mount lighting solutions.*

FLUSH MOUNTS

DAMP **ML184PN**

DAMP **ML183A**

Melon

FINISH: **A** Antique Brass **ES** Empire Silver
PN Palladian Bronze **W** Fresco

GLASS: Etched Melon

ML183ES DAMP

DAMP **ML182PNUL**

DAMP **ML183W**

PRODUCT	DIMENSIONS	BULBS
ML182AUL/ESUL/PNUL/WUL	4.5" H, 10.5" W, 10.5" Dp.	1-75W Med. Base **or** 18W CFL
ML183A/ES/PN/W	5" H, 13" W, 13" Dp.	2-75W Med. Base **or** 18W CFL
ML184A/ES/PN/W	6" H, 15" W, 15" Dp.	3-75W Med. Base **or** 18W CFL

MNR1611BN DAMP

DAMP MNR1613PN

DAMP MNR1613BN

Manor

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze

GLASS: White Alabaster

DAMP MNR1615PN

PRODUCT	DIMENSIONS	BULBS
MNR1611BN/PN	5" H, 11" W, 11" Dp.	1-100W Med. Base **or** 23W CFL
MNR1613BN/PN	5" H, 13" W, 13" Dp.	2-75W Med. Base **or** 18W CFL
MNR1615BN/PN	5.5" H, 15" W, 15" Dp.	3-75W Med. Base **or** 18W CFL

SMT1612PN DAMP

DAMP SMT1614PN

Summit

FINISH: **BN** Brushed Nickel
PN Palladian Bronze
GLASS: Opal

DAMP SMT1614BN

DAMP SMT1617BN

PRODUCT	DIMENSIONS	BULBS
SMT1612BN/PN	4.5" H, 12" W, 12" Dp.	1-100W Med. Base **or** 23W CFL
SMT1614BN/PN	5.5" H, 14" W, 14" Dp.	2-75W Med. Base **or** 18W CFL
SMT1617BN/PN	6" H, 17" W, 17" Dp.	3-75W Med. Base **or** 18W CFL

GF1617AN DAMP

DAMP GF1617PN

Griffin

FINISH: **AN** Antique Nickel
PN Palladian Bronze

GLASS: Etched Painted White Inside

See matching Griffin semi-flush mounts on page 294.

DAMP GF1621AN

GF1621PN DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
GF1617AN/PN	7" H, 17" W, 17" Dp.	6" x 1.25"	3-100W Med. Base **or** 23W CFL
GF1621AN/PN	8.5" H, 21" W, 21" Dp.	6" x 1.25"	4-60W Med. Base **or** 13W CFL

OZ1613IN DAMP

DAMP OZ1613PN

Ozark

FINISH: IN Iron Gate **PN** Palladian Bronze
GLASS: Etched Painted White Inside

See matching Ozark semi-flush mounts on page 293.

OZ1616IN DAMP

DAMP OZ1616PN

PRODUCT	DIMENSIONS	BULBS
OZ1613IN/PN	5.5" H, 13" W, 13" Dp.	2-60W Med. Base **or** 13W CFL
OZ1616IN/PN	6.5" H, 16" W, 16" Dp.	3-60W Med. Base **or** 13W CFL

WLS1613PN DAMP

Wilson

FINISH: Palladian Bronze
GLASS: Clear & Opal Etched

DAMP WLS1615PN

Bound

FINISH: Royal Ebony

*See matching pendant **BND1818BA** on page 268.*



BND1613BA DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
BND1613BA	7" H, 13.5" W, 13.5" Dp.	.75" x 5.25"	3-40W Vintage Bulb Supplied*
WLS1613PN	7" H, 13" W, 13" Dp.	-	2-75W Med. Base **or** 18W CFL
WLS1615PN	7.5" H, 15" W, 15" Dp.	-	3-75W Med. Base **or** 18W CFL

*Max Wattage: 60W Med. Base **or** 18W CFL

Flush Mounts

Please see referenced page numbers for larger images and full descriptions of these products.

Adonis

ADS1615DC

See page 39

Monterey Mosaic

MY1613ML

See page 85

Monterey Mosaic

MY1618ML

See page 85

Chamber

CHB1612DK

See page 106

Laila

LLA1615RA

See page 116

Opera

OPA1613WT

See page 127

Opera

OPA1617WT

See page 127

PLATINUM COLLECTION

Bordeaux

BRX1614C

See page 175

PLATINUM COLLECTION

Bordeaux

BRX1619C

See page 175

PLATINUM COLLECTION

Bordeaux

BRXA1614C

See page 175

PLATINUM COLLECTION

Bordeaux

BRXA1619C

See page 175

PLATINUM COLLECTION

Bordeaux

BRX1611C

See page 176

PLATINUM COLLECTION
Bordeaux
BRX1620C
See page 176



PLATINUM COLLECTION
Bordeaux
BRX1626C
See page 176

PLATINUM COLLECTION
Countess
PCCT1616C
See page 179

PLATINUM COLLECTION
Countess
PCCT1623C
See page 179

PLATINUM COLLECTION
Paragon
PRN1614C
See page 182

PLATINUM COLLECTION
Highrise
PCHE1616C
See page 183

PLATINUM COLLECTION
Highrise
PCHE1620C
See page 183

PLATINUM COLLECTION
Ella
PCEL1616C
See page 184

PLATINUM COLLECTION
Ella
PCEL1623C
See page 184

PLATINUM COLLECTION
Valla
VLA1618C
See page 185

PLATINUM COLLECTION
Ribbons
RBN1616CRC
See page 187

PLATINUM COLLECTION
Ribbons
RBN1622CRC
See page 187

Flush Mounts

Please see referenced page numbers for larger images and full descriptions of these products.

PLATINUM COLLECTION

Ribbons

RBN1628CRC

See page 187

PLATINUM COLLECTION

Ribbons

RBN1616C/MN/SG/W/WT

See page 189

PLATINUM COLLECTION

Ribbons

RBN1622C/MN/SG/W/WT

See page 189



PLATINUM COLLECTION

Ribbons

RBN1628C/MN/SG/W/WT

See page 189



Laguna

MCLG1612RC

See page 229

Laguna

MCLG1616RC

See page 229

Zen

ZE1617K

See page 239

*Please see the **Quoizel Tiffany Collection** on **page 459** for many attractive art glass flush mount lighting solutions.*

From the **DUCHESS COLLECTION: DH1404PN** (p.312)

TRACK LIGHTING

QUOIZEL

Duchess

FINISH: AN Antique Nickel **PN** Palladian Bronze
GLASS: AN Grey Marble **PN** Champagne Marble

Please see pages 52-57 for matching Duchess products.

Also available in PN finish:
DH1404PN DAMP

DAMP DH1404AN

All Quoizel Track Lights Swivel

Kyle

FINISH: Imperial Bronze
SHADE: Butterscotch Onyx

Please see pages 68-73 for matching Kyle products.

QUOIZEL NATURALS ONYX

KY1404IB DAMP

Monterey Mosaic

FINISH: Malaga
SHADE: Pen Shell Mosaic

DAMP MY1404ML

QUOIZEL NATURALS PEN SHELL

Please see pages 81-86 for matching Monterey Mosaic products.

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH1404AN/PN	12.5" H, 36.5" W, 6" Dp.	6.5" x 4.5"	4-100W Med. Base **or** 23W CFL
KY1404IB	14.5" H, 36" W, 4.5" Dp.	8.25" x 4.5"	4-100W Med. Base **or** 23W CFL
MY1404ML	16.5" H, 43.5" W, 5" Dp.	7.25"	4-100W Med. Base **or** 23W CFL

PF1405C DAMP

Please see page 359 for matching Pacifica products.

Pacifica

FINISH: Polished Chrome
GLASS: Opal Etched with Wave Pattern

DAMP QTR10054PN

Denning

FINISH: Palladian Bronze
SHADE: Metal

All Quoizel Track Lights Swivel

DAMP EVE1404PN

Eastvale

FINISH: Palladian Bronze
SHADE: Metal

Please see page 105 for matching Eastvale products.

PRODUCT	DIMENSIONS	CANOPY	BULBS
EVE1404PN	10.5" H, 36.5" W, 3.5" Dp.	7" x 5"	4-50W MR-16 with GU10 Base Shielded Supplied
PF1405C	10.5" H, 44.5" W, 4.5" Dp.	6.5" x 4.5"	5-60W Frosted G9 Halogen Supplied
QTR10054PN	13.5" H, 36" W, 3.5" Dp.	6.5"	4-50W MR-16 with GU10 Base Shielded Supplied

From the **KYLE COLLECTION: KY1404IB** (p. 312)

Asheville

FINISH: Valiant Bronze

Please see pages 470-474 for matching Asheville products.



Track Light converts to an Island Light

TFAS1404VA DAMP

TFIK1404VA DAMP

Inglenook

FINISH: Valiant Bronze

Please see pages 464-468 for matching Inglenook products.

All Quoizel Track Lights Swivel

Victory

FINISH: Valiant Bronze

Please see pages 460-461 for matching Victory products.

NEW!
FOR ◆ 2016

TFVY1404VA DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFAS1404VA	13.5" H*, 43.5" W, 7" Dp.	5.5" x 1.75"	4-100W Med. Base **or** 23W CFL	Each Shade Contains 44 Pieces of Tiffany Glass
TFIK1404VA	14" H, 42" W, 6" Dp.	9.5" x 4.5" x .75"	4-100W Med. Base **or** 23W CFL	Each Shade Contains 184 Pieces of Tiffany Glass
TFVY1404VA	15" H, 43" W, 6" Dp.	6"	4-100W Med. Base **or** 23W CFL	Each Shade Contains 65 Pieces of Tiffany Glass

*Comes with (2) 6" and (2) 12" Rods.

Taylor

FINISH: **AN** Antique Nickel
WT Western Bronze

GLASS: Opal Etched

Please see pages 87-91 for matching Taylor products

NEW!
FOR ◆ 2016

TY1444AN DAMP

NEW!
FOR ◆ 2016

DAMP **TY1444WT**

All Quoizel Track Lights Swivel

TY1404AN DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
TY1404AN	8.5" H, 43" W, 3" Dp.	9" x 4.5" x .875"	4-60W Frosted G9 Halogen Supplied
TY1444AN/WT	11" H, 44" W, 5" Dp.	9" x 4.75"	4-100W Med. Base **or** 23W CFL

From the **DOWNTOWN COLLECTION:** **DW8701C**
(p. 49)

LSM8801GY

LSM8801PS

LSM8801TM

Millenium

FINISH: GY Gallery Gold
PS Pewter Plated
TM Teco Marrone
SHADE: White Parchment

Yuma

FINISH: Imperial Bronze
GLASS: Amber Scavo

YU8710IB

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS	SHADE DIMS
LSM8801GY	10" H, 10" W, 5.5" Dp.	5.5" x 5.75"	3.5"	1-60W Cand. Base	(4.25" x 7") x (5.25" x 10") x 7"
LSM8801PS/TM	10" H, 9" W, 5.5" Dp.	7" x 7"	3.5"	1-60W Cand. Base	7" x 9" x 5.5"
YU8710IB	8.5" H, 17" W, 9" Dp.	4.5"	2.5"	1-100W Med. Base **or** 23W CFL	-

Wall Fixtures

Please see referenced page numbers for larger images and full descriptions of these products.

Adonis
ADS8701DC
See page 38

Downtown
DW8701BN/C
See page 49

Duchess
DH8601AN/PN
See page 57

Kendra
KD8701MM
See page 65

Kyle
KY8701IB/IN
See page 73

Kyle
KY8801IN/IB
See page 73

La Parra
LP8601IB
See page 76

Marquette
MQ8701HL
See page 79

Monterey Mosaic
MY8801ML
See page 86

Taylor
TY8501AN
See page 87

Taylor
TY8601C/AN/BN
See page 91

Trilogy
TRG8701OZ
See page 95

Whitney
WHI8701IS
See page 97

Adams
ADA8702LN
See page 103

Armelle
AME8701IB
See page 109

Remi
REM8701C
See page 123

Wall Fixtures

Please see referenced page numbers for larger images and full descriptions of these products.

Noble

NBE8702RK

See page 129

Tricia

TCA8701VP

See page 137

UPTOWN COLLECTION

East Village

UPEV8701WT

See page 217

UPTOWN COLLECTION

Theater Row

UPTR8701IS/WT

See page 218

UPTOWN COLLECTION

Madison Manor

UPMM8701WT

See page 222



UPTOWN COLLECTION

Seaport

UPSE8701WT

See page 226



UPTOWN COLLECTION

Holita

UPHL8701IS

See page 226

Inglenook

TFIK8802

See page 468

Stephen

TFST8701VB

See page 480

Classic Craftsman

TFCC8802

See page 506

Bath Lighting

*Please see the **Quoizel Bath Lighting Collection** starting on **p. 321** for many additional wall lighting solutions.*

From the **TAYLOR COLLECTION:**
TY8501AN *(p. 87)*

BATH FIXTURES | QUOIZEL

From the
DOWNTOWN COLLECTION:
DW8701C *(p.334)*
Photo Courtesy of
Regina Sturrock Design, Inc.
www.reginasturrockdesign.com

NEW!
FOR ◆ 2016

Quoizel now offers styles that are compatible with retro-fit LED bulbs, styles with LED bulbs supplied and integrated LED products which are indicated by the logo to the right.

INTEGRATED LED
10 YEAR WARRANTY

Bram COLLECTION

FINISH: Polished Chrome
GLASS: o pal etched

NEW!
FOR ◆ 2016



PCBM8520C DAMP

Enlarged for detail

PLATINUM by QUOIZEL

INTEGRATED LED
10 YEAR WARRANTY



DAMP **PCBM8526C**

OPTIC GLASS

PCBM8505C DAMP

LED CHART

	PCBM8505C	PCBM8520C	PCBM8526C
Lumens	880	2138	2996
Total Watts	12W	25.5W	36W
Color Rendering Index (CRI)	90	90	90
Color Temperature (CCT)	2700K	3000K	3000K
Dimmable	Yes	Yes	Yes

Bram COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCBM8505C	13.5" H, 5.5" W, 3.5" Ext.	4.5" x 4.5"	8.75"	See LED chart
PCBM8520C	5.5" H, 20.5" W, 3.5" Ext.	4.5" x 4.5"	3"	See LED chart
PCBM8526C	5.5" H, 26.5" W, 3.5" Ext.	4.5" x 4.5"	3"	See LED chart

Bram bath fixtures can be mounted horizontally or vertically.

Pierre

FINISH: Brushed n ickel
GLASS: o ptic

INTEGRATED LED
10 YEAR WARRANTY

MOUNTS

MOUNTS

DAMP **PCPR8522BN**

Enlarged for detail

DAMP **PCPR8530BN**

LED CHART

	PCPR8522	PCPR8530
Lumens	1800	2200
Total Watts	20W	28W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

DAMP **PCED8517C**

Enlarged for detail

INTEGRATED LED
10 YEAR WARRANTY

MOUNTS

DAMP **PCED8528C**

Endless

FINISH: Polished Chrome
GLASS: o ptic, Sandblasted inside

DAMP **PCED8521C**

LED CHART

	PCED8517	PCED8521	PCED8528
Lumens	1200	1800	2500
Total Watts	12W	18W	25W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3000K	3000K	3000K
Dimmable	Yes	Yes	Yes

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCED8517C	4.5" H, 17.5" W, 4.5" Ext.	17.37" x 4.37"	2.18"	See LED chart
PCED8521C	4.5" H, 21.5" W, 4.5" Ext.	21.25" x 4.37"	2.18"	See LED chart
PCED8528C	4.5" H, 29" W, 4.5" Ext.	28.75" x 4.37"	2.18"	See LED chart
PCPR8522BN	4.5" H, 22" W, 4" Ext.	4.5" x 7"	2.5"	See LED chart
PCPR8530BN	4.5" H, 30" W, 4" Ext.	4.5" x 7"	2.5"	See LED chart

Pierre bath fixtures can be mounted horizontally or vertically.

Valiant

NEW! FOR ◆ 2016

FINISH: Brushed n ickel
GLASS: Clear etched inside



PCVT8518BN DAMP

Enlarged for detail

MOUNTS

PCVT8524BN DAMP

LED CHART

	PCVT8518BN	PCVT8524BN
Lumens	1565	2020
Total Watts	21W	39W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

PLATINUM by QUOIZEL

INTEGRATED LED
10 YEAR WARRANTY

Blade

NEW! FOR ◆ 2016

FINISH: Polished Chrome
GLASS: o pal etched

PCBD8519C DAMP

MOUNTS

PCBD8526C DAMP

Enlarged for detail

LED CHART

	PCBD8519C	PCBD8526C
Lumens	1830	2565
Total Watts	25W	33W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	2700K	2700K
Dimmable	Yes	Yes

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCBD8519C	5" H, 19" W, 4.5" Ext .	4.75" x 6.75"	2.5"	See LED chart
PCBD8526C	5" H, 26" W, 4.5" Ext.	4.75" x 6.75"	2.5"	See LED chart
PCVT8518BN	5" H, 18" W, 3.5" Ext.	4.5" x 5.75"	2.5"	See LED chart
PCVT8524BN	5" H, 24" W, 3.5" Ext.	4.5" x 5.75"	2.5"	See LED chart

Valiant and Blade bath fixtures can be mounted horizontally or vertically.

Pace

FINISH: Polished Chrome
GLASS: Opal Etched Inner, Clear Outer

PCPC8527C DAMP

Enlarged for detail

PLATINUM by QUOIZEL

DAMP **PCPC8533C**

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

	PCPC8527C	PCPC8533C
Lumens	2060	2740
Total Watts	32W	42W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

Promenade

FINISH: Polished Chrome
GLASS: Acrylic Rectangular

PCPE8524C DAMP

Enlarged for detail

MOUNTS

MOUNTS



PCPE8536C DAMP

LED CHART

	PCPE8524C	PCPE8536C
Lumens	960	1440
Total Watts	8W	12W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCPC8527C	4.5" H, 26.5" W, 4" Ext.	7" x 4.5"	2.5"	See LED chart
PCPC8533C	4.5" H, 33" W, 4" Ext.	7" x 4.5"	2.5"	See LED chart
PCPE8524C	4.5" H, 24" W, 3" Ext.	7" x 4.5"	2.5"	See LED chart
PCPE8536C	4.5" H, 37" W, 3" Ext.	7" x 4.5"	2.5"	See LED chart

Promenade bath fixtures can be mounted horizontally or vertically.

PCDH8522BN

PCDH8530BN

Dash

FINISH: Brushed Nickel
GLASS: White

LED CHART

	PCDH8522BN	PCDH8530BN
Lumens	1600	2240
Total Watts	20W	28W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

INTEGRATED LED
10 YEAR WARRANTY

MOUNTS

PCGL8522BN

Enlarged for detail

Glacial

FINISH: Polished Chrome
GLASS: Clear, Sandblasted Inside

MOUNTS

LED CHART

	PCGL8522BN	PCGL8530BN
Lumens	1700	3200
Total Watts	22W	30W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Dimmable	Yes	Yes

PCGL8530BN

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCDH8522BN	4.5" H, 22" W, 3.5" Ext.	21.5" x 4.5"	2.5"	See LED chart
PCDH8530BN	4.5" H, 30" W, 3.5" Ext.	29.5" x 4.5"	2.5"	See LED chart
PCGL8522BN	5" H, 22" W, 5" Ext.	6" x 5"	2.5"	See LED chart
PCGL8530BN	5.5" H, 30" W, 5" Ext.	6.75" x 5.5"	2.5"	See LED chart

Dash and Glacial bath fixtures can be mounted horizontally or vertically.

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

- Dramatic lighting created by faceted crystal pendants
- f ree of contaminant colors such as iron for clarity and purity allowing the light to radiate to its greatest potential
- Bulbs are positioned in the most strategic locations, maximizing the radiance of the light emanating through the crystal
- h ighly polished mirrored chrome maximizes the reflectivity of the projected light
- t he highest quality g 4 and g 9 bulbs create a great intensity of light

PCAX8603CLED DAMP

Enlarged for detail

Alexa

FINISH: Polished Chrome
GLASS: Crystal

*See matching Semi-Flush **PCAX1714C** on page 179.*

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

PCAX8604CLED DAMP

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCAX8603CLED	5" H, 25" W, 4" Ext.	24.37" x 5.12"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
PCAX8604CLED	5" H, 33" W, 4" Ext	32.25" x 5.12"	3"	4-4.5W Frosted G9 LED Dimmable Supplied

Shimmer COLLECTION

FINISH:
Polished Chrome

GLASS:
Crystal studded

PCSR8603CLED

Enlarged for detail

See matching semi-flush ***PCSR1716C*** *on page 181.*

PLATINUM by QUOIZEL

CRYSTAL ◆ COLLECTION

MOUNTS

PCSR8602CLED

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

PCSR8604CLED

Shimmer COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSR8602CLED	8" H, 13.5" W, 5.5" Ext.	4.75" x 4.75"	6"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSR8603CLED	8" H, 23" W, 5.5" Ext.	4.75" x 4.75"	6"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSR8604CLED	8" H, 32" W, 5.5" Ext.	4.75" x 4.75"	6"	4-4.5W Frosted G9 LED Dimmable Supplied

Shimmer bath fixtures can be mounted as uplights or downlights.

Seaview COLLECTION

NEW!
FOR ◆ 2016

FINISH: BN Brushed n ickel **C** Polished Chrome
GLASS: BN Clear t hick etched inside **C** Clear t hick

DAMP PCSW8602CLED

Enlarged for detail

MOUNTS

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

PLATINUM by QUOIZEL

PCSW8601BNLED DAMP

DAMP PCSW8603BNLED

PCSW8604CLED DAMP

Seaview COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSW8601BNLED / CLED	7" H, 5.5" W, 4.5" Ext.	4.75" x 7"	4"	1-4.5W Frosted G9 LED Dimmable Supplied
PCSW8602BNLED / CLED	5.5" H, 14.5" W, 5" Ext.	7" x 4.75"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSW8603BNLED / CLED	5.5" H, 22" W, 5" Ext.	7" x 4.75"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSW8604BNLED / CLED	5.5" H, 30" W, 5" Ext.	7" x 4.75"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Seaview bath fixtures can be mounted as uplights or downlights.

Serena COLLECTION

NEW!
FOR ◆ 2016

FINISH: Brushed n ickel
GLASS: Clear

DAMP **PCSA8602BNLED**

Enlarged for detail

MOUNTS

PLATINUM by QUOIZEL

DAMP **PCSA8603BNLED**

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **PCSA8604BNLED**

Serena COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSA8602BNLED	6.5" H, 12.5" W, 5.5" Ext.	6.75" x 4.75"	5.12"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSA8603BNLED	6.5" H, 20" W, 5.5" Ext.	6.75" x 4.75"	5.12"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSA8604BNLED	6.5" H, 28" W, 5.5" Ext.	6.75" x 4.75"	5.12"	4-4.5W Frosted G9 LED Dimmable Supplied

Serena bath fixtures can be mounted as uplights or downlights.

Lacombe

FINISH: Polished Chrome
SHADE: Metal Frame with Clear Glass Beads

NEW!
FOR ◆ 2016

PCLC8603CLED

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

PCLC8605CLED

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

PCMR8603CLED

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

PCMR8605CLED

Mirabella

NEW!
FOR ◆ 2016

FINISH: Polished Chrome
GLASS: Crystal Accents

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCLC8603CLED	5" H, 18" W, 5.5" Ext.	14.5" x 4.75"	2.5"	3-4.5W Frosted G9 LED Dimmable Supplied
PCLC8605CLED	5" H, 26" W, 6.5"" Ext.	19.5" x 4.75"	2.5"	5-4.5W Frosted G9 LED Dimmable Supplied
PCMR8603CLED	9.5" H, 12" W, 5.5" Ext.	12" x 6"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
PCMR8605CLED	11" H, 24" W, 6" Ext.	24" x 6"	3"	5-4.5W Frosted G9 LED Dimmable Supplied

Lacombe and Mirabella bath fixtures can be mounted as uplights or downlights.

Divine COLLECTION

FINISH: Polished Chrome
GLASS: Clear Crystal

DAMP **PCDV8602CLED**

detail

NEW!
FOR ◆ 2016

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

MOUNTS

PCDV8603CLED DAMP

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **PCDV8604CLED**

Divine COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCDV8602CLED	6" H, 13.5" W, 6" Ext.	7" x 4.75"	5.25"	2-4.5W Frosted G9 LED Dimmable Supplied
PCDV8603CLED	6" H, 23" W, 6" Ext.	7.5" x 4.75"	5.25"	3-4.5W Frosted G9 LED Dimmable Supplied
PCDV8604CLED	6" H, 31.5" W, 6" Ext.	7.5" x 4.75"	5.25"	4-4.5W Frosted G9 LED Dimmable Supplied

Divine bath fixtures can be mounted as uplights or downlights.

Devlin COLLECTION

FINISH: **BN** Brushed n ickel **C** Polished Chrome

GLASS: o pal

DAMP **DVN8602BNLED**

Enlarged for detail



LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

DAMP **DVN8603CLED**

DAMP **DVN8604BNLED**



Devlin COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DVN8602BNLED/CLED NEW!	6" H, 14" W, 8" Ext.	6.5" x 4.5"	3"	2-4.5W Frosted G9 LED Dimmable Supplied
DVN8603BNLED/CLED NEW!	6" H, 22.5" W, 8" Ext.	6.5" x 4.5"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
DVN8604BNLED/CLED NEW!	6" H, 31.5" W, 8" Ext.	6.5" x 4.5"	3"	4-4.5W Frosted G9 LED Dimmable Supplied

Devlin bath fixtures can be mounted as uplights or downlights.

Downtown COLLECTION

FINISH:
BN Brushed n ickel NEW! **C** Polished Chrome

GLASS:
o pal etched

DAMP **DW8603CLED**

DAMP **DW8602CLED**

MOUNTS

DW8701C DAMP

Enlarged for detail

See matching Downtown mirror on page 532

DW8604CLED DAMP

DW8701BN DAMP

NEW! FOR ◆ 2016

DAMP DW8602BNLED

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

(8701 is Non-LED)

MOUNTS

DW8603BNLED DAMP

DAMP DW8604BNLED

Downtown COLLECTION

PRODUCT		DIMENSIONS	CANOPY	HCWO	BULBS
DW8602BNLED/CLED	NEW!	7.5" H, 15" W, 7" Ext.	8" x 5"	5"	2-4.5W Frosted G9 LED Dimmable Supplied
DW8603BNLED/CLED	NEW!	7.5" H, 24.5" W, 7" Ext.	8" x 5"	5"	3-4.5W Frosted G9 LED Dimmable Supplied
DW8604BNLED/CLED	NEW!	7.5" H, 33.5" W, 7" Ext.	8" x 5"	5"	4-4.5W Frosted G9 LED Dimmable Supplied
DW8701BN/C	NEW!	10.5" H, 6" W, 8" Ext.	6" x 6"	7.75"	1-100W Med. Base **or** 23W CFL

Downtown bath fixtures can be mounted as uplights or downlights.

Erin COLLECTION

FINISH: imperial Bronze
GLASS: o pal etched

DAMP **ERN8603IBLED**

Enlarged for detail

MOUNTS

DAMP **ERN8602IBLED**

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **ERN8604IBLED**

Erin COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
ERN8602IBLED NEW!	6" H, 17" W, 5" Ext.	8" x 5"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
ERN8603IBLED NEW!	6" H, 24" W, 5" Ext.	8" x 5"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
ERN8604IBLED NEW!	6" H, 33" W, 5" Ext.	8" x 5"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Erin bath fixtures can be mounted as uplights or downlights.

Tatum COLLECTION

FINISH: Brushed n ickel
GLASS: o pal etched

TU8603BNLED DAMP

Enlarged for detail

TU8602BNLED DAMP

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

TU8604BNLED DAMP

Tatum COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS
TU8602BNLED NEW!	5" H, 13" W, 5.5" Ext.	7" x 4.5"	2.63"	2-4.5W Frosted G9 LED Dimmable Supplied
TU8603BNLED NEW!	5" H, 21" W, 5.5" Ext.	10" x 4.5"	2.63"	3-4.5W Frosted G9 LED Dimmable Supplied
TU8604BNLED NEW!	5" H, 29" W, 5.5" Ext.	18" x 4.5"	2.63"	4-4.5W Frosted G9 LED Dimmable Supplied

Tatum bath fixtures can be mounted as uplights or downlights.

Quinton COLLECTION

FINISH: Polished Chrome

GLASS: o pal etched

DAMP **QI8603CLED**

Enlarged for detail

MOUNTS

QI8602CLED DAMP

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **QI8604CLED**

Quinton COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
QI8602CLED NEW!	9" H, 14" W, 5" Ext.	7" x 5"	6"	2-4.5W Frosted G9 LED Dimmable Supplied
QI8603CLED NEW!	9" H, 23.5" W, 5" Ext.	7" x 5"	6"	3-4.5W Frosted G9 LED Dimmable Supplied
QI8604CLED NEW!	9" H, 33.5" W, 5" Ext.	7" x 5"	6"	4-4.5W Frosted G9 LED Dimmable Supplied

Quinton bath fixtures can be mounted as uplights or downlights.

NolanCOLLECTION

FINISH: Brushed n ickel

GLASS: o pal etched

DAMP **NN8602BNLED**

Enlarged for detail



MOUNTS

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **NN8603BNLED**

DAMP **NN8604BNLED**

NolanCOLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
NN8602BNLED NEW!	5.5" H, 19" W, 6" Ext.	7" x 4.5"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
NN8603BNLED NEW!	5.5" H, 26.5" W, 6" Ext.	7" x 4.5"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
NN8604BNLED NEW!	5.5" H, 35.5" W, 6" Ext.	7" x 4.5"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Nolan bath fixtures can be mounted as uplights or downlights.

Kolt COLLECTION

FINISH: Polished Chrome

GLASS:

o uter: Clear inner: h eavy s andblasted

DAMP **KLT8603CLED**

Enlarged for detail

MOUNTS

DAMP **KLT8602CLED**

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP **KLT8604CLED**

Kolt COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
KLT8602CLED NEW!	6" H, 13" W, 6.5" Ext.	6.5" x 6"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
KLT8603CLED NEW!	6" H, 21" W, 6.5" Ext.	6.5" x 6"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
KLT8604CLED NEW!	6" H, 29" W, 6.5" Ext.	6.5" x 6"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Kolt bath fixtures can be mounted as uplights or downlights.

From the **KOLT COLLECTION:**
KLT8603CLED

Also shown:
GREYSTONE MIRROR: QR1815
(See p.530)

Adano COLLECTION

FINISH: empire silver
GLASS: o pal etched Cased

DAMP **AN8539ES**

Enlarged for detail

MOUNTS

AN8540ES DAMP

DAMP **AN8541ES**

Adano COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
AN8539ES	7.5" H, 14" W, 7" Dp.	8" x 4.5"	3"	2-100W Med. Base **or** 23W CFL
AN8540ES	7.5" H, 21" W, 7" Dp.	8" x 4.5"	3"	3-100W Med. Base **or** 23W CFL
AN8541ES	7.5" H, 28" W, 7" Dp.	8" x 4.5"	3"	4-100W Med. Base **or** 23W CFL

Adano bath fixtures can be mounted as uplights or downlights.

Broadgate COLLECTION

FINISH: Brushed n ickel
GLASS: Clear o pal

DAMP **BGT8602BN**

Enlarged for detail

MOUNTS

DAMP **BGT8603BN**

DAMP **BGT8604BN**

Broadgate COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
BGT8602BN	10" H, 17.5" W, 9" Dp.	5.25" x 5.25"	5.5"	2-100W Med. Base **or** 23W CFL
BGT8603BN	10" H, 27" W, 9" Dp.	5.25" x 5.25"	5.5"	3-100W Med. Base **or** 23W CFL
BGT8604BN	10" H, 36" W, 9" Dp.	5.25" x 5.25"	5.5"	4-100W Med. Base **or** 23W CFL

Broadgate bath fixtures can be mounted as uplights or downlights.

From the **DUBLIN COLLECTION**
Bath Fixture: **DBN8603BN**

Dublin COLLECTION

FINISH:
Brushed n ickel

GLASS:
Clear Pressed

See matching mini-pendant ***DBN1506BN*** *on page 282.*

DBN8602BN DAMP

MOUNTS

NEW! FOR ◆ 2016

DBN8603BN DAMP

DAMP **DBN8604BN**

Dublin COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS
DBN8602BN	9" H, 16" W, 8" Ext.	8" x 4.5"	4.5"	2-100W Med. Base **or** 23W CFL
DBN8603BN	9" H, 25" W, 8" Ext.	8" x 4.5"	4.5"	3-100W Med. Base **or** 23W CFL
DBN8604BN	9" H, 34.5" W, 8" Ext.	8" x 4.5"	4.5"	4-100W Med. Base **or** 23W CFL

Bower bath fixtures can be mounted as uplights or downlights.

Bower COLLECTION

FINISH:
Brushed n ickel

GLASS:
o pal etched

BWR8603BN

Enlarged for detail

MOUNTS

BWR8602BN

BWR8604BN

Bower COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
BWR8602BN	9.5" H, 13" W, 7" Dp.	5" x 5"	7"	2-100W Med. Base **or** 23W CFL
BWR8603BN	9.5" H, 21.5" W, 7" Dp.	5" x 5"	7"	3-100W Med. Base **or** 23W CFL
BWR8604BN	9.5" H, 28.5" W, 7" Dp.	5" x 5"	7"	4-100W Med. Base **or** 23W CFL

Bower bath fixtures can be mounted as uplights or downlights.

DuchessCOLLECTION

FINISH:
AN a ntique n ickel **PN** Palladian Bronze

GLASS:
AN g rey Marble **PN** Champagne Marble

DH8601PN DAMP

See matching Duchess styles on page 52-57

See matching Duchess mirrors on page 530

DH8603AN DAMP

Enlarged for detail

DH8602PN DAMP

MOUNTS

DH8604AN DAMP

DuchessCOLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DH8601AN/PN	11" H, 6" W, 8" Ext.	4.75" x 6.75"	7.5"	1-100W Med. Base **or** 23W CFL
DH8602AN/PN	11" H, 16" W, 7.5" Ext.	9" x 5"	7.5"	2-100W Med. Base **or** 23W CFL
DH8603AN/PN	11" H, 23" W, 7.5" Ext.	9" x 5"	7.5"	3-100W Med. Base **or** 23W CFL
DH8604AN/PN	11" H, 31.5" W, 7.5" Ext.	9" x 5"	7.5"	4-100W Med. Base **or** 23W CFL

Duchess bath fixtures can be mounted as uplights or downlights. Duchess mirrors can be hung vertically or horizontally.

Hollister COLLECTION

FINISH: Polished Chrome
GLASS: o pal etched

DAMP **HS8603C**

Enlarged for detail

HS8602C DAMP

MOUNTS

HS8604C DAMP

DAMP **HS8601C**

Hollister COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
HS8601C	9.5" H, 5" W, 7.5" Ext.	5" x 7"	5.5"	1-100W Med. Base **or** 23W CFL
HS8602C	9.5" H, 14.5" W, 7.5" Ext.	6.75" x 4.75"	7"	2-100W Med. Base **or** 23W CFL
HS8603C	9.5" H, 23" W, 7.5" Ext.	6.75" x 4.75"	7"	3-100W Med. Base **or** 23W CFL
HS8604C	9.5" H, 32.5" W, 7.5" Ext.	6.75" x 4.75"	7"	4-100W Med. Base **or** 23W CFL

Hollister bath fixtures can be mounted as uplights or downlights.

DeluxeCOLLECTION

FINISH: Polished Chrome

GLASS: White linen

DAMP **DX8601C**

*See matching island light **DX348C** on p. 261 and semi-flush **DX1718C** on p. 290.*

DAMP **DX8602C**

MOUNTS

DX8603C DAMP

Enlarged for detail

DAMP **DX8604C**

DeluxeCOLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DX8601C	9" H, 6" W, 7.5" Ext.	4.5" x 6.5"	7"	1-100W Med. Base **or** 23W CFL
DX8602C	10" H, 18" W, 7.5" Ext.	6.25" x 4.5"	8"	2-100W Med. Base **or** 23W CFL
DX8603C	10" H, 25.5" W, 7.5" Ext.	6.25" x 4.5"	8"	3-100W Med. Base **or** 23W CFL
DX8604C	10" H, 33.5" W, 7.5" Ext.	6.25" x 4.5"	8"	4-100W Med. Base **or** 23W CFL

Deluxe bath fixtures can be mounted as uplights or downlights.

Edison COLLECTION

FINISH: Western Bronze
GLASS: seedy



DAMP **EDS8602WT**

DAMP **EDS8601WT**

Enlarged for detail

MOUNTS

DAMP **EDS8603WT**

EDS8604WT DAMP

Edison COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
EDS8601WT	10" H, 5" W, 6.5" Ext.	5" x 5"	8.5"	1-60W Vintage Bulb Supplied*
EDS8602WT	10" H, 16" W, 5.5" Ext.	7.5" x 4.5"	8.5"	2-60W Vintage Bulb Supplied*
EDS8603WT	10" H, 23" W, 7" Ext.	7.5" x 4.5"	8.5"	3-60W Vintage Bulb Supplied*
EDS8604WT	10" H, 32.5" W, 7" Ext.	7.5" x 4.5"	8.5"	4-60W Vintage Bulb Supplied*

Edison bath fixtures can be mounted as uplights or downlights. *Max Wattage: 100W Med. Base **or** 23W CFL.

Garrison COLLECTION

FINISH:
BN Brushed n ickel **WT** Western Bronze

GLASS:
o pal etched

NEW!
FOR ◆ 2016

DAMP **GRN8603BN**

MOUNTS

*See matching Garrison mini-pendants **QPP2049BN/WT** on page 279.*

GRN8602WT DAMP

GRN8604WT DAMP

Garrison COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
GRN8602BN/WT	7" H, 16.5" W, 9" Ext.	9" x 4.5"	4"	2-100W Med. Base **or** 23W CFL
GRN8603BN/WT	7" H, 25" W, 9" Ext.	9" x 4.5"	4"	3-100W Med. Base **or** 23W CFL
GRN8604BN/WT	7" H, 33.5" W, 9" Ext.	9" x 4.5"	4"	4-100W Med. Base **or** 23W CFL

Garrison bath fixtures can be mounted as uplights or downlights.

Demitri COLLECTION

FINISH: Polished Chrome

GLASS: White seedy sandstone

MOUNTS

DI8502C DAMP

Enlarged for detail

DI8503C DAMP

DAMP **DI8504C**

Demitri COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DI8502C	8" H, 18" W, 8" Ext.	8" x 4.5"	5.5"	2-100W Med. Base **or** 23W CFL
DI8503C	8.5" H, 26" W, 8" Ext.	8" x 4.5"	5.5"	3-100W Med. Base **or** 23W CFL
DI8504C	8.5" H, 35.5" W, 8" Ext.	8" x 4.5"	5.5"	4-100W Med. Base **or** 23W CFL

Demitri bath fixtures can be mounted as uplights or downlights.

From the
DEMITRI COLLECTION
Bath Fixture: **DI8503ES**

Demitri COLLECTION

FINISH: empire silver
GLASS: opal etched

DI8503ES DAMP

Enlarged for detail

MOUNTS

DI8502ES DAMP

DAMP **DI8504ES**

Demitri COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DI8502ES	8" H, 18" W, 8" Ext.	8" x 4.5"	5.5"	2-100W Med. Base **or** 23W CFL
DI8503ES	8.5" H, 26" W, 8" Ext.	8" x 4.5"	5.5"	3-100W Med. Base **or** 23W CFL
DI8504ES	8.5" H, 35.5" W, 8" Ext.	8" x 4.5"	5.5"	4-100W Med. Base **or** 23W CFL

Demitri bath fixtures can be mounted as uplights or downlights.

Loft COLLECTION

FINISH: Polished Chrome

GLASS: Clear sandblasted inside

LFT8603C

Enlarged for detail

MOUNTS

LFT8602C

LFT8604C

Loft COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
LFT8602C	7.5" H, 15" W, 6.5" Ext.	6" x 4.5"	5.5"	2-100W Med. Base **or** 23W CFL
LFT8603C	7.5" H, 24" W, 6.5" Ext.	6" x 4.5"	5.5"	3-100W Med. Base **or** 23W CFL
LFT8604C	7.5" H, 34" W, 6.5" Dp.	6" x 4.5"	5.5"	4-100W Med. Base **or** 23W CFL

Loft bath fixtures can be mounted as uplights or downlights.

Melody COLLECTION

FINISH: Brushed Nickel
GLASS: Mottled t extured

DAMP **MLD8603BN**

Enlarged for detail

detail

DAMP **MLD8602BN**

MOUNTS

DAMP **MLD8604BN**

Melody COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
MLD8602BN	6.5" H, 15" W, 5.5" Ext.	9" x 5.75"	3.5"	2-100W Med. Base **or** 23W CFL
MLD8603BN	6.5" H, 24" W, 5.5" Ext.	9" x 5.75"	3.5"	3-100W Med. Base **or** 23W CFL
MLD8604BN	6.5" H, 33" W, 5.5" Ext.	9" x 5.75"	3.5"	4-100W Med. Base **or** 23W CFL

Melody bath fixtures can be mounted as uplights or downlights.

Menlo COLLECTION

FINISH:
imperial silver

*See matching chandelier **MNO5006WT** on page 167.*

NEW!
FOR ◆ 2016

MNO8602IS DAMP

Enlarged for detail

MOUNTS

MNO8603IS DAMP

DAMP **MNO8604IS**

Menlo COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS
MNO8602IS	9" H, 12.5" W, 4.5" Ext.	5.25" x 5.25"	7"	2-60W Vintage Bulbs Supplied*
MNO8603IS	9" H, 21" W, 4.5" Ext.	5.25" x 5.25"	6"	3-60W Vintage Bulbs Supplied*
MNO8604IS	9" H, 30.5" W, 4.5" Ext.	5.25" x 5.25"	6"	4-60W Vintage Bulbs Supplied*

Menlo bath fixtures can be mounted as uplights or downlights. *Max Wattage: 100W Med. Base **or** 23W CFL

From the **PACIFICA COLLECTION:**
PF8603ES

Pacifica COLLECTION

FINISH: empire silver

GLASS: o pal etched with Wave Pattern

MOUNTS

PF8602ES DAMP

Enlarged for detail

See matching track light ***PF1405C*** *on page 313.*

DAMP **PF8603ES**

DAMP **PF8604ES**

Pacifica COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PF8602ES	6.5" H, 16" W, 6.5" Ext.	6.5" x 4.5"	4.5"	2-100W Med. Base **or** 23W CFL
PF8603ES	6.5" H, 25" W, 6.5" Ext.	6.5" x 4.5"	4.5"	3-100W Med. Base **or** 23W CFL
PF8604ES	6.5" H, 33.5" W, 6.5" Ext.	6.5" x 4.5"	4.5"	4-100W Med. Base **or** 23W CFL

Pacifica bath fixtures can be mounted as uplights or downlights.

Nicholas COLLECTION

FINISH:
BN Brushed n ickel **C** Polished Chrome **HO** h arbor Bronze

GLASS:
o pal etched

DAMP **NL8602C**

DAMP **NL8601H0**

Enlarged for detail

DAMP **NL8604C**

DAMP **NL8603BN**

Enlarged for detail

MOUNTS

Nicholas COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
NL8601BN/C/HO	10" H, 5" W, 7" Ext.	4.5" x 8"	5"	1-100W Med. Base **or** 23W CFL
NL8602BN/C/HO	10" H, 15" W, 7" Ext.	8" x 4.5"	3.5"	2-100W Med. Base **or** 23W CFL
NL8603BN/C/HO	10" H, 22" W, 7" Ext.	8" x 4.5"	3.5"	3-100W Med. Base **or** 23W CFL
NL8604BN/C/HO	10" H, 30.5" W, 7" Ext.	8" x 4.5"	3.5"	4-100W Med. Base **or** 23W CFL

Nicholas bath fixtures can be mounted as uplights or downlights.

NorthGate COLLECTION

FINISH:
Brushed n ickel

GLASS:
o pal etched

DAMP **NGT8603BN**



NGT8602BN DAMP

Enlarged for detail

MOUNTS

DAMP **NGT8604BN**

NorthGate COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
NGT8602BN	7" H, 12" W, 6" Ext.	8" x 5"	4"	2-100W Med. Base **or** 23W CFL
NGT8603BN	7" H, 20" W, 6" Ext.	8" x 5"	4"	3-100W Med. Base **or** 23W CFL
NGT8604BN	7" H, 27.5" W, 6" Ext.	8" x 5"	4"	4-100W Med. Base **or** 23W CFL

North Gate bath fixtures can be mounted as uplights or downlights.

Parallel COLLECTION

FINISH: Polished n ickel
GLASS: o pal etched

DAMP **PRL8603PK**

MOUNTS

DAMP **PRL8601PK**

PRL8602PK DAMP

Parallel COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PRL8601PK	8.5" H, 8.5" W, 5.5" Ext.	6" x 4.5"	5.75"	1-100W Med. Base **or** 23W CFL
PRL8602PK	8.5" H, 19" W, 5.5" Ext.	8" x 4.5	5.75"	2-100W Med. Base **or** 23W CFL
PRL8603PK	8.5" H, 30" W, 5.5" Ext.	8" x 4.5	5.75"	3-100W Med. Base **or** 23W CFL

Parallel bath fixtures can be mounted as uplights or downlights.

Supreme COLLECTION

FINISH:
Polished Chrome

GLASS:
etched with Painted White inside

NEW!
FOR ◆ 2016

DAMP **SPR8601C**

SPR8602C DAMP

MOUNTS

SPR8604C DAMP

CRYSTAL FINIALS

SPR8603C DAMP

Enlarged for detail

Supreme COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
SPR8601C	8" H, 5" W, 5.5" Ext.	4.75" x 8"	4.25	1-100W Med. Base **or** 23W CFL
SPR8602C	8" H, 14.5" W, 5.5" Ext.	4.75" x 8"	5.5	2-100W Med. Base **or** 23W CFL
SPR8603C	8" H, 22" W, 5.5" Ext.	4.75" x 8"	5.5	3-100W Med. Base **or** 23W CFL
SPR8604C	8" H, 31" W, 5.5" Ext.	4.75" x 8"	5.5	4-100W Med. Base **or** 23W CFL

Supreme bath fixtures can be mounted as uplights or downlights.

Tritan COLLECTION

FINISH:
Brushed n ickel

GLASS:
o pal etched

DAMP **TT8743BN** *Enlarged for detail*

TT8742BN DAMP

MOUNTS

DAMP **TT8604BN**

Tritan COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
TT8604BN	10" H, 30.5" W, 7.5" Ext.	9" x 4.5"	6"	4-100W Med. Base **or** 23W CFL
TT8742BN	9" H, 13" W, 7.5" Ext.	9" x 4.5"	6"	2-100W Med. Base **or** 23W CFL
TT8743BN	9" H, 22" W, 7.5" Ext.	9" x 4.5"	6"	3-100W Med. Base **or** 23W CFL

Tritan bath fixtures can be mounted as uplights or downlights.

Tranquil Bay COLLECTION

FINISH:
Polished Chrome

GLASS:
o pal etched

DAMP **TB8601C**

Enlarged for detail

MOUNTS

TB8602C DAMP

DAMP **TB8603C**

DAMP **TB8604C**

Tranquil Bay COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
TB8601C	6.5" H, 9" W, 7" Ext.	5" x 5"	4"	1-100W Med. Base **or** 23W CFL
TB8602C	6.5" H, 18" W, 7" Ext.	5" x 5"	4"	2-100W Med. Base **or** 23W CFL
TB8603C	6.5" H, 26" W, 7" Ext.	5" x 5"	4"	3-100W Med. Base **or** 23W CFL
TB8604C	6.5" H, 34" W, 7" Ext.	5" x 5"	4"	4-100W Med. Base **or** 23W CFL

Tranquil Bay bath fixtures can be mounted as uplights or downlights.

From the **TAYLOR COLLECTION**
Bath Fixture: **TY8603AN** Mirror: **TY43625AN**

Taylor COLLECTION

FINISH:
AN a ntique n ickel **BN** Brushed n ickel NEW!
C Polished Chrome **WT** Western Bronze
GLASS: o pal etched

DAMP **TY8601AN**

DAMP **TY8603BN**

Enlarged for detail

NEW!
FOR ◆ 2016

MOUNTS

See matching Taylor mirror on page 530

DAMP **TY8602BN**

detail

DAMP **TY8604WT**

Taylor COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
TY8601AN/BN/C	7.5" H, 4.5" W, 5.5" Dp.	4.5" x 5"	5"	1-100W Med. Base **or** 23W CFL
TY8602AN/BN/C/WT	7.5" H, 13.5" W, 4.5" Dp.	7" x 4.5"	5.5"	2-100W Med. Base **or** 23W CFL
TY8603AN/BN/C/WT	7.5" H, 21" W, 5.5" Dp.	7" x 4.5"	5.5"	3-100W Med. Base **or** 23W CFL
TY8604AN/BN/C/WT	7.5" H, 30" W, 5.5" Dp.	7" x 4.5"	5.5"	4-100W Med. Base **or** 23W CFL

Taylor bath fixtures can be mounted as uplights or downlights.

Paragon COLLECTION

FINISH:
Polished Chrome

*See matching flush mount **PRN1614C** on page 182.*

CRYSTAL STRANDS

DAMP **PRN8606C**

Enlarged for detail

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION



DAMP **PRN8604C**

DAMP **PRN8608C**

Paragon COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PRN8604C	4.5" H, 14.5" W, 4" Ext.	7" x 5"	2.5"	4-20W Clear G4 Xenon Supplied
PRN8606C	5" H, 21.5" W, 4" Ext.	7" x 5"	2.5"	6-20W Clear G4 Xenon Supplied
PRN8608C	5" H, 28.5" W, 4" Ext.	7" x 5"	2.5"	8-20W Clear G4 Xenon Supplied

Evermore COLLECTION

FINISH: Polished Chrome
SHADE: Crystal

DAMP **EME8604C**

Enlarged for detail

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

FACETED CRYSTALS

DAMP **EME8606C**

DAMP **EME8608C**

Evermore COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
EME8604C	5" H, 16" W, 6" Ext.	7" x 4.5"	2.5"	4-20W Clear G4 Xenon Supplied
EME8606C	5" H, 23.5" W, 6" Ext.	7" x 4.5"	2.5"	6-20W Clear G4 Xenon Supplied
EME8608C	5" H, 31" W, 6" Ext.	7" x 4.5"	2.5"	8-20W Clear G4 Xenon Supplied

Royale COLLECTION

FINISH: Polished Chrome
SHADE: Crystal

DAMP **RYE8604C** *Enlarged for detail*

PLATINUM by QUOIZEL
CRYSTAL ◆ COLLECTION

FACETED CRYSTALS

detail

DAMP **RYE8605C**

Royale COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
RYE8604C	5" H, 20" W, 5" Ext.	7" x 4.5"	2.5"	4-20W Clear G4 Xenon Supplied
RYE8605C	5" H, 24" W, 5" Ext.	7" x 4.5"	2.5"	5-20W Clear G4 Xenon Supplied

From the **BOOKER COLLECTION:**
BKR8408K (p. 404-405)

QUOIZEL

OUTDOOR**LIGHTING**

Monument COLLECTION

FINISH:
Western Bronze

NEW!
FOR ◆ 2016

CERAMIC TILE ACCENT

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	475
Total Watts	5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

MNT8404WT WET

WET **MNT8405WT**

Monument COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
MNT8404WT	14" H, 5" W, 4" Dp.	5.25" x 5.25"	7"	See LED chart
MNT8405WT	17.5" H, 6" W, 4" Dp.	5.25" x 5.25"	8.5"	See LED chart

Newbury COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Seedy

NEW!
FOR ◆ 2016

NYL1911K DAMP

INDOOR OUTDOOR

WET NYL8407K

NYL8409K WET

LED CHART

NYL8407K / NYL8409K

Lumens	880
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

INTEGRATED LED
10 YEAR WARRANTY

S·O·L·I·D BRASS

NYL8411K WET

Enlarged for detail

WET NYL9011K

LED CHART

NYL1911K / NYL8411K / NYL9011K

Lumens	1280
Total Watts	16W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

Newbury COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	Light Source
NYL1911K	19" H , 10.5" W, 10.5" Dp.	5"	-	See LED chart
NYL8407K	12" H, 7" W, 7" Ext	4.75" x 5.5"	6"	See LED chart
NYL8409K	13.5" H, 8" W, 8" Ext	4.75" x 5.5"	7"	See LED chart
NYL8411K	20" H, 10.5" W, 10" Ext	4.5" x 9.25"	10"	See LED chart
NYL9011K	21" H, 11" W, 11" Dp.	-	-	See LED chart

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Newbury COLLECTION

FINISH:
K Mystic Black **P** Pewter **Z** Medici Bronze

GLASS:
Clear Seedy

Our Newbury Collection is available in attractive SEEDY glass in 3 finishes!

WET NY8416Z

TITLE 24 WET NY8407P

S·O·L·I·D BRASS

NY8409K WET TITLE 24

NY8411P WET

NY1615K DAMP

WET NY8412Z

NY1909Z DAMP

NY1912P DAMP

NY1916K DAMP

INDOOR OUTDOOR

S·O·L·I·D BRASS

NY9011K WET

WET NY9012P

WET NY9016Z

Newbury COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	FINISHES
NY1615	8" H, 15.5" W, 15.5" Dp.	14"	-	3-40W Cand. Base	K, P, Z
NY1909	19" H , 10.5" W, 10.5" Dp	5"	-	2-60W Cand. Base	K, P, Z
NY1912	21" H, 12.5" W, 12.5" Dp.	5"	-	3-60W Cand. Base	K, P, Z
NY1916	26.5" H, 16" W, 16" Dp.	5"	-	4-60W Cand. Base	K, P, Z
NY8407	12" H, 7" W, 7" Dp.	4.75" x 5.5"	6"	1-150W Med. Base **or** 40W CFL	K, P, Z
NY8409	13.5" H, 8" W, 8" Ext.	4.75" x 5.5"	7"	1-150W Med. Base **or** 40W CFL	K, P, Z
NY8411	20" H, 10.5" W, 10" Ext.	4.5" x 9.25"	10"	2-60W Cand. Base	K, P, Z
NY8412	22.5" H, 12.5" W, 11.5" Ext.	4.5" x 9.25"	10"	3-60W Cand. Base	K, P, Z
NY8416	29" H , 16" W, 15" Ext.	5.25" x 12.5"	12"	4-60W Cand. Base	K, P, Z
NY9011	21" H, 11" W x 11" Dp.	-	-	2-60W Cand. Base	K, P, Z
NY9012	23" H, 12" W, 12" Dp.	-	-	3-60W Cand. Base	K, P, Z
NY9016	29.5" H, 16" W, 16" Dp.	-	-	4-60W Cand. Base	K, P, Z

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Finishes Guide:

K=Mystic Black **P**=Pewter **Z**=Medici Bronze

TITLE 24 To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Newbury COLLECTION

One of our most popular and expansive outdoor lines, the **Newbury Collection,** *is available in 12 styles, each style in a number of attractive finishes. As we can only show a partial representation on these pages, please refer to the chart on the next page as a complete resource for dimensions and bulb/wattage information.*

WET **NY8339P**

S·O·L·I·D BRASS

NY8317B WET

Finish: Polished Brass
Glass: Clear Beveled

NY8315B WET TITLE 24

S·O·L·I·D BRASS

DAMP **NY1794Z**

Finish: Medici Bronze
Glass: Clear Beveled

WET **NY9042Z**

The Newbury products on these pages represent a sampling of the 12 different styles offered in 6 different finishes.

Please refer to the chart below for dimensions and bulb/wattage information.

Newbury COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	FINISHES
NY1178	19" H, 11" W, 11" Dp.	5"	-	2-60W Cand. Base	A, AC, B, K, P, Z
NY1179	21" H, 12.5" W, 12.5" Dp.	5"	-	3-60W Cand. Base	A, AC, B, K, P, Z
NY1180	26.5" H, 16" W, 16" Dp.	5"	-	4-60W Cand. Base	A, AC, B, K, P, Z
NY1794	8" H, 15.5" W, 15.5" Dp.	-	-	3-40W Cand. Base	B, K, P, Z
NY8315	12.5" H, 7" W, 7" Ext.	4.75" x 5.5"	6"	1-150W Med. Base **or** 40W CFL	A, AC, B, K, P, Z
NY8316	14" H, 9" W, 8" Ext.	4.75" x 5.5"	7"	1-150W Med. Base **or** 40W CFL	A, AC, B, K, P, Z
NY8317	20" H, 11" W, 10" Ext.	4.5" x 9.25"	10"	2-60W Cand. Base	A, AC, B, K, P, Z
NY8318	22.5" H, 12.5" W, 11.5" Ext.	4.5" x 9.25"	10"	3-60W Cand. Base	A, AC, B, K, P, Z
NY8339	29" H , 16" W, 15" Ext.	5.25" x 12.5"	12"	4-60W Cand. Base	A, AC, B, K, P, Z
NY9042	21" H, 11" W x 11" Dp.	-	-	2-60W Cand. Base	A, AC, B, K, P, Z
NY9043	23" H, 12.5" W, 12.5" Dp.	-	-	3-60W Cand. Base	A, AC, B, K, P, Z
NY9045	30.5" H, 16" W, 16" Dp.	-	-	4-60W Cand. Base	A, AC, B, K, P, Z

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Finishes Guide:

A=Antique Brass **AC**=Aged Copper **B**=Polished Brass
K=Mystic Black **P**=Pewter **Z**=Medici Bronze

TITLE 24 To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Newbury COLLECTION

WET NY9045K

WET NY8318K

S·O·L·I·D BRASS

Finish: Mystic Black
Glass: Clear Beveled

The Newbury products on these pages represent a sampling of the 12 different styles offered in 6 different finishes.

Please refer to the chart on page 377 for dimensions and bulb/wattage information.

DAMP NY1178A

Finish: Antique Brass
Glass: Clear Beveled

NY9043A WET

S·O·L·I·D BRASS

NY8317P WET

Finish: Pewter
Glass: Clear Beveled

TITLE 24 WET **NY8316P**

S·O·L·I·D BRASS

The Newbury products on these pages represent a sampling of the 12 different styles offered in 6 different finishes.

Please refer to the chart on page 377 for dimensions and bulb/wattage information.

NY1180AC DAMP

Finish: Aged Copper
Glass: Clear Beveled

NY1179AC DAMP

S·O·L·I·D COPPER

Outdoor exposure will naturally darken the hue of copper products over time.

ALT8407WT WET

ALT8405WT WET

Alto

FINISH: Western Bronze
GLASS: Clear Seedy

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

	ALT8405WT	ALT8407WT	RYD8408WT
Lumens	825	1645	1028
Total Watts	10W	21W	15W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3000K	3000K	3000K
Dimmable	Yes	Yes	Yes

Ryland

FINISH: Western Bronze
GLASS: Opal etched

WET RYD8408WT

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
ALT8405WT	15" H, 5.5" W, 5.5" Ext.	4.5" x 6.5"	7.5"	See LED Chart
ALT8407WT	20" H, 7" W, 7" Ext.	5" x 8.5"	8"	See LED Chart
RYD8408WT	13" H, 8" W, 4" Ex.	4.75" x 4.75"	11"	See LED Chart

Cole

FINISH: Western Bronze

ETCHED GLASS

COE8305WT WET

COE8405WT WET

INTEGRATED LED

10 YEAR WARRANTY

LED CHART

COE8305WT / COE8405WT

Lumens	1985
Total Watts	12W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	Yes

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
COE8305WT	10" H, 5" W, 5" Ext.	4.5" x 4.5"	5"	See LED Chart
COE8405WT	13" H, 5" W, 5.5" Ext.	4.5" x 5"	6.5"	See LED Chart

Stonington COLLECTION

FINISH:
K Mystic Black **PN** Palladian Bronze

GLASS:
Clear Water

NEW!
FOR ◆ 2016

COASTAL ARMOUR
by QUOIZEL

5 YEAR WARRANTY

SNNL8409K

With a core-strengthening ingredient of natural quarry stone crushed to a fine powder and then mixed with a powerful blend of latex and adhesives, ***Coastal Armour by Quoizel*** *creates the next generation of products by using a material of extraordinary strength, durability and beauty.*

Our Coastal Armour composite material has been tested to withstand extreme heat and brutal cold; it is non-corrosive (acid and alkali-resistant) and UV resistant – both properties that make it stronger than the best resin products. That is why we are offering a 5 year warranty. Our unique synthetic composite formula allows us to fabricate our designs in high pressure injected steel molds that produce a superior quality of detail while increasing surface durability.

Coastal Armour by Quoizel *will ensure many years of enjoyment with our beautiful outdoor products.*

INTEGRATED LED
10 YEAR WARRANTY

INDOOR OUTDOOR

SNNL1909PN DAMP

LED CHART

SNNL8406K

Lumens	880
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

SNNL8406K WET

LED CHART

SNNL1909K/PN / SNNL8408K/PN
SNNL8409K/PN / SNNL9009K/PN

Lumens	1280
Total Watts	16W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

SNNL8408K WET

WET SNNL9009PN

StoningtonCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SNNL1909K/PN	15" H, 9.5" W, 9.5" Dp.	1" x 5.125"	-	See LED Chart
SNNL8406K/PN	10.5" H, 6.5" W, 7.5" Ext.	4.5" x 6.5"	3.5"	See LED Chart
SNNL8408K/PN	13" H, 8" W, 9.5" Ext.	4.5" x 6.5"	3.5"	See LED Chart
SNNL8409K/PN	15.5" H, 9.5" W, 10.5" Ext.	4.5" x 8"	4"	See LED Chart
SNNL9009K/PN	16.5" H, 9.5" W, 9.5" Ext.	-	-	See LED Chart

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Stonington COLLECTION

FINISH:
K Mystic Black **PN** Palladian Bronze **W** Fresco NEW!

GLASS:
Clear Water

COASTAL ARMOUR by QUOIZEL

5 YEAR WARRANTY

SNN8409W

NEW!
FOR ◆ 2016

DAMP SNN1612W

NEW!
FOR ◆ 2016

NEW!
FOR ◆ 2016

TITLE 24 DAMP SNN1909PN

INDOOR OUTDOOR

TITLE 24 WET SNN8406W

Available in 3 finishes!

SNN8408PN WET TITLE 24

TITLE 24 WET SNN9009K

Stonington COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SNN1612K/PN/W	6" H, 12" W, 12" Dp.	1" x 12"	-	2-60W Med. Base **or** 13W CFL
SNN1909K/PN/W	15" H, 9.5" W, 9.5" Dp.	1" x 5.125"	-	1-100W Med. Base **or** 23W CFL
SNN8406K/PN/W	10.5" H, 6.5" W, 7.5" Ext.	4.5" x 6.5"	3.5"	1-100W Med. Base **or** 23W CFL
SNN8408K/PN/W	13" H, 8" W, 9.5" Ext.	4.5" x 6.5"	2.5"	1-100W Med. Base **or** 23W CFL
SNN8409K/PN/W	15.5" H, 9.5" W, 10.5" Ext.	4.5" x 8"	2.5"	1-100W Med. Base **or** 23W CFL
SNN9009K/PN/W	16.5" H, 9.5" W, 9.5" Dp.	-	-	1-100W Med. Base **or** 23W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Cathedral COLLECTION

FINISH:
Palladian Bronze

GLASS:
Clear Seedy

NEW!
FOR ◆ 2016

COASTAL ARMOUR
by QUOIZEL

5 YEAR WARRANTY

CATL8411PN WET

CATL1911PN (DAMP)

INDOOR OUTDOOR

CATL8407PN (WET)

LED CHART

CATL8407PN

Lumens	880
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

CATL1911PN / CATL8409PN
CATL8411PN / CATL9011PN

Lumens	1280
Total Watts	16W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

CATL8409PN (WET)

CATL9011PN (WET)

Cathedral COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	LIGHT SOURCE
CATL1911PN	18.5" H, 11.5" W, 8.5" Dp.	5.125"	-	See LED Chart
CATL8407PN	11" H, 7.5" W, 6.5" Dp.	4.75" x 6.5"	3.5"	See LED Chart
CATL8409PN	13.5" H, 9.5" W, 8" Dp.	4.75" x 8"	4"	See LED Chart
CATL8411PN	16.5" H, 11.5" W, 9.5" Dp.	4.75" x 8"	4"	See LED Chart
CATL9011PN	19" H, 11.5" W, 8.5" Dp.	-	-	See LED Chart

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Cathedral COLLECTION

FINISH:
Palladian Bronze

GLASS:
Clear Seedy

NEW!
FOR ◆ 2016

COASTAL ARMOUR
by QUOIZEL

5 YEAR WARRANTY

CAT8411PN WET

CAT1911PN DAMP

INDOOR OUTDOOR

WET CAT8407PN

CAT8409PN WET

WET CAT9011PN

Cathedral COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
CAT1911PN	18.5" H, 11.5" W, 8.5" Dp.	5.125"	-	1-150W Med. Base **or** 40W CFL
CAT8407PN	11" H, 7.5" W, 6.5" Ext.	4.75" x 6.5"	3.5"	1-100W Med. Base **or** 23W CFL
CAT8409PN	13.5" H, 9.5" W, 8" Ext.	4.75" x 8"	4"	1-100W Med. Base **or** 23W CFL
CAT8411PN	16.5" H, 11.5" W, 9.5" Ext.	4.75" x 8"	4"	1-150W Med. Base **or** 40W CFL
CAT9011PN	19" H, 11.5" W, 8.5" Dp.	-	-	1-150W Med. Base **or** 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

FortQuinnCOLLECTION

FINISH:
AW Antique Brown **MK** Marcado Black

GLASS:
Amber Seedy

FQ8414AW WET

FQ8411AW WET

FQ8407MK WET TITLE 24

COASTAL ARMOUR by QUOIZEL

5 YEAR WARRANTY

TITLE 24 WET FQ8409MK

WET FQ9011AW

FortQuinn COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
FQ8407AW/MK	15" H, 7" W, 9" Ext.	6.5" x 4.75"	6.5"	1-100W Med. Base **or** 23W CFL
FQ8409AW/MK	19" H , 9" W, 11.5" Ext.	8" x 4.75"	8.5"	1-100W Med. Base **or** 23W CFL
FQ8411AW/MK	23" H, 11" W, 14.5" Ext.	8" x 4.75"	11"	3-60W Cand. Base
FQ8414AW/MK*	30" H, 14" W, 18" Ext.	7.125" x 11"	15"	4-60W Cand. Base
FQ9011AW/MK	19" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

***FQ8414AW/MK is not Coastal Armour and is not covered by the 5 Year Warranty.**

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only

FortQuinn COLLECTION

FINISH:
Marcado Black

FQ1931MK01

INDOOR OUTDOOR

FQ1920MK01

FortQuinn COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
FQ1920MK01*	41" H, 19" W, 19" Dp.	5"	4-60W Cand. Base
FQ1931MK01*	52" H, 31" W, 31" Dp.	5"	8-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.
***FQ1920MK01 and FQ1931MK01 are not Coastal Armour and are not covered by the 5 Year Warranty.**

From the **FORT QUINN COLLECTION:**
FQ8407MK

Bedford COLLECTION

FINISH:
K Mystic Black **PN** Palladian Bronze

GLASS:
Clear Seedy

COASTAL ARMOUR by QUOIZEL

5 YEAR WARRANTY

TITLE 24 WET **BFD8410K**

BFD1910K DAMP TITLE 24

INDOOR OUTDOOR

TITLE 24 WET BFD8407PN

BFD8408K WET TITLE 24

TITLE 24 WET BFD9010PN

Bedford COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
BFD1910K/PN	18" H, 10" W, 10" Dp.	5.25"	-	1-150W Med. Base **or** 40W CFL
BFD8407K/PN	13" H, 7" W, 8" Ext.	5.5" x 6.75"	3.75"	1-100W Med. Base **or** 23W CFL
BFD8408K/PN	15.5" H, 8.5" W, 9.5" Ext.	6.5" x 8"	3.75"	1-100W Med. Base **or** 23W CFL
BFD8410K/PN	18.5" H, 10" W, 11" Ext.	7.5" x 9.25"	4.25"	1-150W Med. Base **or** 40W CFL
BFD9010K/PN	19" H, 10" W, 10" Dp.	-	-	1-150W Med. Base **or** 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Tudor COLLECTION

FINISH:
K Mystic Black **PN** Palladian Bronze

GLASS:
Clear Seedy

COASTAL ARMOUR
by QUOIZEL

5 YEAR WARRANTY

TITLE 24 WET **TDR8409PN**

TDR1909K DAMP TITLE 24

INDOOR OUTDOOR

TDR8406PN WET TITLE 24

TDR8408PN WET TITLE 24

TITLE 24 WET TDR9009PN

Tudor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TDR1909K/PN	14.5" H, 9.5" W, 9.5" Dp.	5.12"	-	1-150W Med. Base **or** 40W CFL
TDR8406K/PN	10.5" H, 6.5" W, 7.5" Ext.	6.5" x 4.62"	2.75"	1-100W Med. Base **or** 23W CFL
TDR8408K/PN	12.5" H, 8" W, 9" Ext.	6.5" x 4.62"	2.75"	1-100W Med. Base **or** 23W CFL
TDR8409K/PN	15" H, 9.5" W, 10.5" Ext.	8" x 4.75"	2.75"	1-150W Med. Base **or** 40W CFL
TDR9009K/PN	16" H, 9.5" W, 9.5" Dp.	-	-	1-150W Med. Base **or** 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Marblehead COLLECTION

FINISH:
K Mystic Black **PN** Palladian Bronze

GLASS:
Clear Seedy

COASTAL ARMOUR by QUOIZEL

5 YEAR WARRANTY

WET **MBH8411K**

Marblehead COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
MBH8411K/PN	17.5" H, 11" W, 12" Ext.	8" x 5.5"	3.5"	3-60W Cand. Base

From the **MARBLEHEAD COLLECTION:**
MBH8407PN

Marblehead COLLECTION

FINISH:
K Mystic Black
PN Palladian Bronze

GLASS:
Clear Seedy

TITLE 24 WET **MBH8407PN**

MBH1911PN DAMP

INDOOR OUTDOOR

COASTAL ARMOUR by QUOIZEL

5 YEAR WARRANTY

MBH8409K WET

WET **MBH9011K**

Marblehead COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MBH1911K/PN	18" H, 11" W, 11" Dp.	5"	-	3-60W Cand. Base
MBH8407K/PN	11" H, 7" W, 8" Ext.	6.5" x 4.5"	3"	1-100W Med. Base **or** 23W CFL
MBH8409K/PN	14.5" H, 9" W, 10" Ext.	8" x 5.5"	3.5"	3-60W Cand. Base
MBH9011K/PN	19" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Crestview COLLECTION

FINISH:
Western Bronze

GLASS:
Clear Seedy

NEW!
FOR ◆ 2016

CVW8406WT

CVW8408WT

CVW8407WT

Crestview COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
CVW8406WT	12.5" H, 6" W, 5" Ext.	5" x 4.75"	4.75"	1-60W Vintage Bulb Supplied*
CVW8407WT	15.5" H, 7" W, 6" Ext.	6" x 6"	4.75"	1-60W Vintage Bulb Supplied*
CVW8408WT	18.5" H, 8" W, 6.5" Ext.	6" x 6"	6"	1-60W Vintage Bulb Supplied**

*Max. Wattage: 100W Med. Base **or** 23W CFL. **Max. Wattage: 150W Med. Base **or** 40W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Miles COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Water

NEW!
FOR ◆ 2016

MLS8407IB

MLS1907IB DAMP TITLE 24

INDOOR OUTDOOR

MLS8406IB WET TITLE 24

MLS8405IB WET TITLE 24

TITLE 24 WET MLS9007IB

Miles COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MLS1907IB	20" H, 7.5" W, 7.5" Dp.	4.5"	-	1-150W Medium Base **or** 40W CFL
MLS8405IB	16.5" H, 5.5" W, 7" Ext.	7" x 4.5"	6.5"	1-100W Med. Base **or** 23W CFL
MLS8406IB	19" H, 6.5" W, 8.5" Ext.	9" x 5"	8"	1-100W Med. Base **or** 23W CFL
MLS8407IB	21.5" H, 7.5" W, 9.5" Ext.	9" x 5"	8.5"	1-150W Medium Base **or** 40W CFL
MLS9007IB	19.5" H, 7.5" W, 7.5" Dp.	-	-	1-150W Medium Base **or** 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Booker COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Seedy

NEW!
FOR ◆ 2016

BKR8410K

BKR1910K

BKR8406K

INDOOR OUTDOOR

BKR8408K

BKR9010K

Booker COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
BKR1910K	18" H, 10.5" W, 9" Dp.	5"	-	1-60W Vintage Bulb Supplied**
BKR8406K	11.5" H, 7" W, 6.5" Ext.	7" x 4.5"	4.5"	1-60W Vintage Bulb Supplied*
BKR8408K	15" H, 9" W, 8.5" Ext.	7" x 4.5"	5.25"	1-60W Vintage Bulb Supplied*
BKR8410K	18.5" H, 11" W, 10" Ext.	7" x 4.5"	6.5"	1-60W Vintage Bulb Supplied**
BKR9010K	19.5" H, 10.5" W, 10.5" Dp.	-	-	1-60W Vintage Bulb Supplied**

Outdoor hanging fixtures come with 12' of wire and 8' of chain. *Max. Wattage: 100W Med. Base **or** 23W CFL. **Max. Wattage: 150W Med. Base **or** 40W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Hunter COLLECTION

FINISH:
imperial Bronze

GLASS:
l ight Amber

HTR8408IB

HTR1908IB DAMP TITLE 24

HTR8406IB WET TITLE 24

HTR8407IB WET TITLE 24

TITLE 24 WET HTR9008IB

HunterCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
HTR1908IB	19" H, 8.5" W, 8.5" Dp.	5"	-	1-150W Med. Base **or** 40W CFL
HTR8406IB	11.5" H, 6" W, 7" Ext.	4.625" x 4.625"	2.5"	1-100W Med. Base **or** 23W CFL
HTR8407IB	15" H, 7.5" W, 8.5" Ext.	6" x 6"	3"	1-100W Med. Base **or** 23W CFL
HTR8408IB	18.5" H, 8.5" W, 9.5" Ext.	7.125" x 7.125"	3.5"	1-150W Med. Base **or** 40W CFL
HTR9008IB	21" H, 8.5" W, 8.5" Dp.	-	-	1-150W Med. Base **or** 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Oasis COLLECTION

FINISH:
Medici Bronze

GLASS:
Clear Beveled

WET **OAS8413Z**

S·O·L·I·D BRASS

OAS1909Z DAMP

TITLE 24 WET OAS8406Z

S·O·L·I·D BRASS

WET OAS8411Z

OAS8408Z WET

WET OAS8409Z

OAS9009Z WET

OAS9011Z WET

Oasis COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
OAS1909Z	20.5" H, 9" W, 9" Dp.	5"	-	3-60W Cand. Base
OAS8406Z	17" H, 5.5" W, 7.5" Ext.	6" x 4.5"	8.5"	1-100W Med. Base **or** 23W CFL
OAS8408Z	21" H, 7.5" W, 9" Ext.	6" x 4.5"	9.5"	2-60W Cand. Base
OAS8409Z	23" H, 9" W, 11" Ext.	6" x 4.5"	9.5"	3-60W Cand. Base
OAS8411Z	26" H, 11" W, 12.5" Ext.	8.25" x 5.375"	11"	4-60W Cand. Base
OAS8413Z	33" H, 14" W, 15.5" Ext.	10" x 6"	14"	5-60W Cand. Base
OAS9009Z	22" H, 9" W, 9" Dp.	-	-	3-60W Cand. Base
OAS9011Z	26.5" H, 11" W, 11" Dp.	-	-	4-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Harmony COLLECTION

FINISH:
imperial Bronze

GLASS:
Cream l inen

HY8413IB

TITLE 24

- CFL Spring Self-Ballasted GU 24

Not Shown:

HY8407IBFL
HY8507IBFL
1-23W CFL

HY8409IBFL
HY8509IBFL
1-23W CFL

HY8513IBFL
1-23W CFL

CAST *Aluminum*

HY1911IB DAMP

CAST *Aluminum*

HY8409IB WET TITLE 24

HY8407IB WET TITLE 24

HY8411IB WET

WET HY9011IB

Harmony COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
HY1911IB	20.5" H, 11" W, 11" Dp.	5"	-	3-60W Cand. Base
HY8407IB	10.5" H, 6.5" W, 8" Ext.	5" x 8.75"	2.38"	1-100W Med. Base **or** 23W CFL
HY8409IB	14" H, 9" W, 11" Ext.	5" x 11.25"	4.25"	1-150W Med. Base **or** 40W CFL
HY8411IB	17.5" H, 11" W, 13.5" Ext.	6" x 13.5"	4"	3-60W Cand. Base
HY8413IB	20.5" H, 13" W, 15.5" Ext.	6" x 13.5"	4"	1-150W Med. Base **or** 40W CFL
HY9011IB	20.5" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Hillcrest COLLECTION

FINISH:
imperial Bronze

GLASS:
Translucent l inen

HC8413IB WET TITLE 24

CAST *Aluminum*

TITLE 24

- CFL Spring Self-Ballasted GU 24

Not Shown:

HC1109IBFL
HC1909IBFL
1-23W CFL

HC1913IBFL
1-23W CFL

HC8406IBFL
HC8506IBFL
1-23W CFL

HC8407IBFL
HC8507IBFL
1-23W CFL

HC8409IBFL
HC8509IBFL
1-23W CFL

HC8411IBFL
HC8511IBFL
1-23W CFL

HC8413IBFL
HC8513IBFL
1-23W CFL

HC9011IBFL
HC9111IBFL
1-23W CFL

HC9013IBFL
1-23W CFL

HCE8409IBFL
HCE8509IBFL
1-23W CFL

HCE8411IBFL
HCE8511IBFL
1-23W CFL

HC8409IB

HC8411IB

HC8407IB

CAST *Aluminum*

HC8406IB

HCE8409IB

HCE8411IB

Hillcrest COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
HC8406IB	9.5" H, 6" W, 7" Ext.	4.5" x 4.5"	2.5"	1-100W Med. Base **or** 23W CFL
HC8407IB	10" H, 7" W, 8" Ext.	4.5" x 7"	2.5"	1-150W Med. Base **or** 40W CFL
HC8409IB	12.5" H, 9" W, 10" Ext.	4.5" x 7"	2.75"	1-150W Med. Base **or** 40W CFL
HC8411IB	15.5" H, 11" W, 12" Ext.	4.5" x 7"	2.75"	1-150W Med. Base **or** 40W CFL
HC8413IB	17.5" H, 13" W, 14" Ext.	4.5" x 10"	2.75"	1-150W Med. Base **or** 40W CFL
HCE8409IB	20" H, 9" W, 10" Ext.	5" x 13"	6.5"	1-150W Med. Base **or** 40W CFL
HCE8411IB	25.5" H, 11" W, 12" Ext.	5" x 16"	8"	1-150W Med. Base **or** 40W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

From the **HILLCREST COLLECTION**
Wall Lantern: **HC8413IB**

Hillcrest COLLECTION

FINISH:
imperial Bronze

GLASS:
Translucent l inen

HC1909IB DAMP TITLE 24

HC1612IB DAMP TITLE 24

CAST *Aluminum*

HC1913IB DAMP TITLE 24

TITLE 24 WET **HC9011IB**

HC9013IB WET TITLE 24

Hillcrest COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
HC1612IB	7" H, 11.5" W, 11.5" Dp.	-	2-60W Med. Base **or** 13W CFL
HC1909IB	13" H, 9" W, 9" Dp.	4.5"	1-150W Med. Base **or** 40W CFL
HC1913IB	18" H, 13" W, 13" Dp.	4.5" x 4.5"	1-150W Med. Base **or** 40W CFL
HC9011IB	19" H, 11" W, 11" Dp.	-	1-150W Med. Base **or** 40W CFL
HC9013IB	19.5" H, 13" W, 13" Dp.	-	1-150W Med. Base **or** 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Lodge COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Hammered

LDG8409K

LDG8406K WET TITLE 24

TITLE 24 WET LDG8408K

TITLE 24 WET LDG9009K

TITLE 24 DAMP LDG1909K

Lodge COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
LDG1909K	13.5" H, 9.5" W, 9.5" Dp.	5.12"	-	1-100W Med. Base **or** 23W CFL
LDG8406K	9" H, 6.5" W, 7.5" Ext.	4.37" x 4.37"	3.5"	1-100W Med. Base **or** 23W CFL
LDG8408K	10.5" H, 8" W, 9" Ext.	4.37" x 4.37"	3.5"	1-100W Med. Base **or** 23W CFL
LDG8409K	12.5" H, 9.5" W, 10.5" Ext.	6.5" x 4.5"	5"	1-100W Med. Base **or** 23W CFL
LDG9009K	16" H, 9.5" W, 9.5" Dp.	-	-	1-100W Med. Base **or** 23W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Millhouse COLLECTION

FINISH:
K Mystic Black **VN** Veneto NEW!

GLASS:
Clear Seedy

NEW!
FOR ◆ 2016

MHE8410VN WET

MHE1910K DAMP

MHE8406VN WET TITLE 24

NEW!
FOR ◆ 2016

WET MHE8409VN

NEW!
FOR ◆ 2016

WET MHE9010K

Millhouse COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MHE1910K/VN	19" H, 10" W, 10" Dp.	5"	-	3-60W Cand. Base
MHE8406K/VN	15.5" H, 7" W, 7.5" Ext.	4.5" x 6"	6"	1-100W Med. Base **or** 23W CFL
MHE8409K/VN	18.5" H, 8" W, 8.5" Ext.	4.5" x 6"	8"	2-60W Cand. Base
MHE8410K/VN	22" H, 10" W, 10.5" Ext.	8" x 5"	9.5"	3-60W Cand. Base
MHE9010K/VN	21.5" H, 10" W, 10" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

The Charleston Copper Lantern Collection gives you the historic look of gas lighting. Charleston Copper Lanterns are all electric, solid copper and hand riveted giving your home the romantic, reproduction style of antique gas lights still popular today on many of the charming homes in Charleston and New Orleans.

From the **RUE DE ROYAL COLLECTION**
Wall Lantern: **RO8414AC** WET

Rue de Royale COLLECTION

FINISH:
Aged Copper

GLASS:
Clear

RO1914AC DAMP

RO8311AC WET

RO8411AC WET

S·O·L·I·D COPPER

RO8410AC WET TITLE 24

RO9014AC WET

Rue de Royal COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
RO1914AC	29.5" H, 27.5" W, 27.5" Dp.	5"	-	4-60W Cand. Base
RO8311AC	23.5" H, 10.5" W, 13" Ext.	5" x 5"	10.5"	2-60W Cand. Base
RO8410AC	20.5" H, 9.5" W, 11" Ext.	5" x 5"	10.5"	1-100W Med. Base **or** 23W CFL
RO8411AC	22" H, 10.5" W, 13" Ext.	5" x 5"	10.5"	2-60W Cand. Base
RO8414AC	29" H, 13.5" W, 16" Ext.	5" x 5"	14"	4-60W Cand. Base
RO9014AC	26" H, 17" W, 15.5" Dp.	-	-	4-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Outdoor exposure will naturally darken the hue of copper products over time.

Chalmers COLLECTION

FINISH:
Aged Copper

GLASS:
Clear

CM8408AC

CM1912AC

S·O·L·I·D COPPER

CM9012AC

CM8412AC

Chalmers COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
CM1912AC	26" H, 12" W, 12" Dp.	5.5"	-	3-60W Cand. Base
CM8408AC	15.5" H, 8" W, 9" Ext.	8" x 5.5"	8"	1-100W Med. Base **or** 23W CFL
CM8410AC	19" H, 10" W, 11.5" Ext.	8" x 5.5"	8"	2-60W Cand. Base
CM8412AC	23" H, 12" W, 13.5" Ext.	8" x 5.5"	11"	3-60W Cand. Base
CM9012AC	26" H, 12" W, 12" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Outdoor exposure will naturally darken the hue of copper products over time.

CHARLESTON
COPPER LANTERN COLLECTION
BY QUOIZEL

The Charleston Copper Lantern Collection gives you the historic look of gas lighting. Charleston Copper Lanterns are all electric, solid copper and hand riveted giving your home the romantic, reproduction style of antique gas lights still popular today on many of the charming homes in Charleston and New Orleans.

From the **CHALMERS COLLECTION**
Wall Lantern: **CM8410AC** WET

Cooper COLLECTION

FINISH:
CU Copper Bronze **K** Mystic Black

GLASS:
Clear Seedy

COR8412K

COR1611K

COR1611CU

COR8409K

COR8410K

COR9010K

CooperCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
COR1611CU/K	10.5" H, 11.5" W, 11.5" Dp.	1" x 7"	-	1-100W Med. Base **or** 23W CFL
COR8409K	17.5" H, 9" W, 11" Ext.	4" x 5.5"	12"	1-100W Med. Base **or** 23W CFL
COR8410K	21" H, 10" W, 12" Ext.	4.5" x 7"	13"	1-100W Med. Base **or** 23W CFL
COR8412K	24.5" H, 12" W, 13" Ext.	4.5" x 8.5"	13"	1-150W Med. Base **or** 40W CFL
COR9010K	18" H, 10" W, 10" Dp.	-	-	1-100W Med. Base **or** 23W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Marine COLLECTION

FINISH:
Western Bronze

GLASS:
Clear Seedy



WET **MRE8410WT**

MRE1909WT DAMP TITLE 24

MRE1506WT DAMP

INDOOR OUTDOOR

TITLE 24 WET MRE8406WT

TITLE 24 WET MRE8409WT

MRE8408WT WET TITLE 24

TITLE 24 WET MRE9009WT

Marine COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MRE1506WT	12" H*, 6" W, 6" Dp.	6"	-	1-60W Vintage Bulbs Supplied†
MRE1909WT	20" H, 9.5" W, 9.5" Dp.	.75" x 6"	-	1-60W Vintage Bulbs Supplied†
MRE8406WT	11.5" H, 6.5" W, 7" Ext.	5" x 6.37"	4"	1-60W Vintage Bulbs Supplied†
MRE8408WT	15" H, 8.5" W, 9" Ext.	4.75" x 9"	5"	1-60W Vintage Bulbs Supplied†
MRE8409WT	17" H, 9.5" W, 11" Ext.	4.75" x 9"	5.5"	1-60W Vintage Bulbs Supplied†
MRE8410WT	20" H, 11" W, 11.5" Ext.	9" x 4.75"	5.5"	3-40W Vintage Bulbs Supplied††
MRE9009WT	23" H, 11" W, 11" Dp.	-	-	1-60W Vintage Bulbs Supplied†

Outdoor hanging fixtures come with 12' of wire and 8' of chain. *Comes with (2) 6" and (2) 12" rods. †Max. Wattage: 100W Med. Base **or** 23W CFL. ††Max. Wattage: 60W Cand. Base.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Devon COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Beveled

CAST
Aluminum

DE8961IB WET

DE1490IB DAMP

WET DE8959IB

WET DE8960IB

DE8976IB WET

WET DE9256IB

TITLE 24 WET DE8958IB

Devon COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
DE1490IB	31" H, 11" W, 11" Dp.	5.5"		3-60W Cand. Base
DE8958IB	12.5" H, 7" W, 8.5" Ext.	4.75" x 7.75"	4"	1-150W Med. Base **or** 40W CFL
DE8959IB	21" H, 9" W, 11" Ext.	5" x 10"	14"	2-60W Cand. Base
DE8960IB	26" H, 11" W, 14" Ext.	5" x 12"	17.5"	3-60W Cand. Base
DE8961IB	25" H, 11" W, 14" Ext.	5" x 12"	4"	3-60W Cand. Base
DE8976IB	21" H, 9" W, 11" Ext.	5" x 10"	5"	2-60W Cand. Base
DE9256IB	23" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Ridge COLLECTION

FINISH:
Western Bronze

GLASS:
Clear

RGE8411WT WET TITLE 24

CAST *Aluminum*



RGE1911WT

INDOOR OUTDOOR

RGE8407WT

RGE8409WT

RGE9011WT

Ridge COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
RGE1911WT	19" H, 11" W, 9.5" Dp.	4.375"	-	1-60W Vintage Bulb Supplied*
RGE8407WT	12.5" H, 7" W, 7" Ext.	6.5" x 4.5"	3.5"	1-60W Vintage Bulb Supplied**
RGE8409WT	16" H, 9" W, 8.5" Ext.	7" x 4.5"	5.5"	1-60W Vintage Bulb Supplied**
RGE8411WT	19" H, 11" W, 10.5" Ext.	9" x 5"	5.5"	1-60W Vintage Bulb Supplied*
RGE9011WT	21.5" H, 11" W, 9.5" Dp.	-	-	1-60W Vintage Bulb Supplied*

Outdoor hanging fixtures come with 12' of wire and 8' of chain. *Max Wattage: 100W Med. Base **or** 25W CFL. **Max Wattage: 150W Med. Base **or** 40W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Rutledge COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Beveled

S·O·L·I·D
BRASS

WET **RJ8414K**

RJ1911K DAMP

INDOOR OUTDOOR

WET RJ8409K

TITLE 24 WET RJ8407K

RJ8411K WET

WET RJ9011K

Rutledge COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
RJ1911K	19.5" H, 11" W, 11" Dp.	5"	-	3-60W Cand. Base
RJ8407K	15" H, 7" W, 8.5" Ext.	4.75" x 7"	7"	1-150W Med. Base **or** 40W CFL
RJ8409K	19" H, 9" W, 10" Ext.	4.75" x 7"	9"	2-60W Cand. Base
RJ8411K	24" H, 11" W, 12.5" Ext.	5" x 9.5"	11.5"	3-60W Cand. Base
RJ8414K	29" H, 13.5" W, 15.5" Ext.	5" x 12.5"	14.5"	4-60W Cand. Base
RJ9011K	20.5" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Byron COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Beveled



BRN8412IB

BRN1910IB DAMP TITLE 24

INDOOR OUTDOOR

TITLE 24 WET BRN8408IB

TITLE 24 WET BRN8406IB

BRN8410IB WET TITLE 24

TITLE 24 WET BRN9010IB

Byron COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
BRN1910IB	20.5" H, 10" W, 7" Dp.	4.5" x 4.5"	-	1-60W Vintage Bulb Supplied*
BRN8406IB	12" H, 6.5" W, 5.5" Ext.	5.75" x 4"	3"	1-60W Vintage Bulb Supplied*
BRN8408IB	14.5" H, 8" W, 7" Ext.	6.5" x 4"	3.5"	1-60W Vintage Bulb Supplied*
BRN8410IB	18" H, 10" W, 8.5" Ext.	9" x 5"	5"	1-60W Vintage Bulb Supplied*
BRN8412IB	21.5" H, 12" W, 8.5" Ext.	9" x 5"	15"	2-60W Vintage Bulbs Supplied*
BRN9010IB	21" H, 10" W, 10" Dp.	3.25"	-	1-60W Vintage Bulb Supplied*

Outdoor hanging fixtures come with 12' of wire and 8' of chain. *Max Wattage: 100W Med. Base **or** 23W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Steadman COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Seedy

CAST *Aluminum*

TITLE 24 WET **SDN8409IB**

SDN1908IB DAMP TITLE 24

INDOOR OUTDOOR

SDN1506IB DAMP

TITLE 24 WET SDN8407IB

WET TITLE 24 SDN8408IB

SDN8405IB WET TITLE 24

TITLE 24 WET SDN9008IB

Steadman COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SDN1506IB	12" H*, 5.5" W, 5.5" Dp.	5"	-	1-60W Vintage Bulb Supplied**
SDN1908IB	21" H, 8.5" W, 8.5" Dp.	5"	-	1-60W Vintage Bulb Supplied**
SDN8405IB	12.5" H, 6" W, 7" Ext.	5.5" x 5.5"	4.75"	1-60W Vintage Bulb Supplied**
SDN8407IB	16" H, 7" W, 8.5" Ext.	6.5" x 6.5"	6"	1-60W Vintage Bulb Supplied**
SDN8408IB	19.5" H, 8" W, 10.5" Ext.	6.5" x 6.5"	7.5"	1-60W Vintage Bulb Supplied**
SDN8409IB	23" H, 10" W, 11.5" Ext.	8.5" x 8.5"	9"	2-60W Vintage Bulbs Supplied**
SDN9008IB	20.5" H, 8.5" W, 11.5" Dp.	-	-	1-60W Vintage Bulb Supplied**

Chain-hung fixture comes with 12' of wire and 8' of chain. *Comes with (2) 6" and (2) 12" rods. **Max Wattage: 100W Med. Base **or** 23W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Galen COLLECTION

FINISH:
imperial Bronze

GLASS:
u mber l inen

CAST *Aluminum*

GLN8412IB

Galen COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
GLN8412IB	14.5" H, 11.5" W, 10" Ext.	7" x 4.5"	4"	1-150W Med. Base **or** 40W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

From the **GALEN COLLECTION**
GLN8409IB

Galen COLLECTION

FINISH:
imperial Bronze

GLASS:
u mber l inen

GLN1910IB

GLN8409IB

INDOOR OUTDOOR

GLN8407IB

CAST *Aluminum*

GLN8410IB

Enlarged for detail

GLN9010IB

Galen COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
GLN1910IB	13.5" H, 10" W, 10" Dp.	4.5" x 4.5"	-	1-150W Med. Base **or** 40W CFL
GLN8407IB	7.5" H, 6.5" W, 6" Dp.	5.5" x 4.5"	2.75"	1-100W Med. Base **or** 23W CFL
GLN8409IB	10" H, 8.5" W, 7.5" Ext.	7" x 4.5"	3.5"	1-150W Med. Base **or** 40W CFL
GLN8410IB	12" H, 10" W, 8.5" Dp.	7" x 4.5"	3.5"	1-150W Med. Base **or** 40W CFL
GLN9010IB	15" H, 10" W, 10" Dp.	-	-	1-150W Med. Base **or** 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

ChancellorCOLLECTION

FINISH:
Copper Bronze

GLASS:
Clear

CCR8406CU

CCR8408CU

CCR9010CU

CCR8410CU

ChancellorCOLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
CCR8406CU	11.5" H, 5.5" W, 6.5" Ext.	5" x 4"	4"	1-100W Med. Base **or** 23W CFL
CCR8408CU	19" H, 8" W, 9" Ext.	6" x 5"	7.5"	2-60W Cand. Base
CCR8410CU	23.5" H, 11" W, 11" Ext.	7.5" x 5.5"	11"	3-60W Cand. Base
CCR9010CU	22" H, 10" W, 10" Dp.	-	-	3-60W Cand. Base

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Trumbull COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Seedy

WET **TML8408K**

TML1908K DAMP

INDOOR OUTDOOR

TML8405K WET

TML8407K WET

WET TML9008K

Trumbull COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TML1908K	19" H, 8.5" W, 8.5" Dp.	1" x 5"		3-60W Cand. Base
TML8405K	14.5" H, 5.5" W, 6" Ext.	4.5" x 4.5"	9.5"	1-60W Cand. Base
TML8407K	18.5" H, 7" W, 8" Ext.	5" x 5"	12.5"	2-60W Cand. Base
TML8408K	22.5" H, 8.5" W, 9.5" Ext.	5.5" x 5.5"	15"	2-60W Cand. Base
TML9008K	21.5" H, 8.5" W, 8.5" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Province COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Seedy

CAST *Aluminum*

PRV8409K WET

PRV1909K DAMP

INDOOR OUTDOOR

PRV8406K WET TITLE 24

PRV8408K WET

WET PRV9009K

Province COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
PRV1909K	15.5" H, 9.5" W, 9.5" Dp.	4.5"	-	3-60W Cand. Base
PRV8406K	15.5" H, 6.5" W, 8" Ext.	6.5" x 4.5"	6.75"	1-100W Med. Base **or** 23W CFL
PRV8408K	17.5" H, 8.5" W, 9.5" Ext.	6.5" x 4.5"	7.5"	2-60W Cand. Base
PRV8409K	19" H, 9.5" W, 10.5" Ext.	7" x 4.5"	7.5"	3-60W Cand. Base
PRV9009K	18" H, 9.5" W, 9.5" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Powell COLLECTION

FINISH:
Western Bronze

GLASS:
White Art

PWL8311WT

PWL8309WT

PWL8307WT

PWL1613WT

PWL9009WT

Powell COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PWL1613WT	6" H, 13" W, 13" Dp.	9" x 5"	-	3-75W Med. Base **or** 18W CFL
PWL8307WT	13.5" H, 7" W, 5" Ext.	9" x 5"	8"	1-100W Med. Base **or** 23W CFL
PWL8309WT	17" H, 9" W, 5.5" Ext.	9" x 5"	11"	1-150W Med. Base **or** 40W CFL
PWL8311WT	20.5" H, 11" W, 6.5" Ext.	11" x 5"	13"	1-150W Med. Base **or** 40W CFL
PWL9009WT	20.5" H, 4.5" W, 9" Dp.	-	-	1-150W Med. Base **or** 40W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

From the **BAIN COLLECTION:**
Wall Lantern: **BAN8411K**

Bain COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Beveled

S·O·L·I·D BRASS

WET **BAN8411K**

Bain COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
BAN8411K	22" H, 11" W, 10" Ext.	7" x 4.75"	7.75"	3-60W Cand. Base

Bain COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Beveled

BAN8407K

DAMP BAN1911K

INDOOR OUTDOOR

S·O·L·I·D BRASS

BAN9011K WET

WET BAN8409K

Bain COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
BAN1911K	20.5" H, 11.5" W, 11.5" Dp.	5"	-	3-60W Cand. Base
BAN8407K	15" H, 7.5" W, 7" Ext.	5.75" x 4.5"	6.5"	1-100W Med. Base **or** 23W CFL
BAN8409K	18" H, 9.5" W, 8.5" Ext.	7" x 4.75"	7.5"	2-60W Cand. Base
BAN9011K	23" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Seaford COLLECTION

FINISH: imperial Bronze

SFD8407IB WET TITLE 24

TITLE 24 DAMP SFD1911IB

TITLE 24 WET SFD8409IB

SFD8411IB WET TITLE 24

INDOOR OUTDOOR

Seaford COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SFD1911IB	8" H*, 11" W, 11" Dp.	5.75"	-	1-100W Med. Base **or** 23W CFL
SFD8407IB	8.5" H, 7" W, 8.5" Ext.	5.75" x 5.75"	4"	1-100W Med. Base **or** 23W CFL
SFD8409IB	9" H, 9" W, 10.5" Ext.	5.75" x 5.75"	5"	1-100W Med. Base **or** 23W CFL
SFD8411IB	11" H, 11" W, 12.5" Ext.	5.75" x 5.75"	5"	1-100W Med. Base **or** 23W CFL

Rod-hung fixtures come with 12' of wire. *Comes with (2) 6" and (2) 12" Rods.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Grover COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Water

CAST *Aluminum*

GVR8410K

GVR1910K DAMP TITLE 24

INDOOR OUTDOOR

TITLE 24 WET GVR8406K

CAST *Aluminum*

GVR8408K WET TITLE 24

TITLE 24 WET GVR9010K

Grover COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
GVR1910K	17.5" H, 10.5" W, 10.5" Dp.	4.5"	-	1-150W Med. Base **or** 40W CFL
GVR8406K	11" H, 6.5" W, 7.5" Ext.	6.5" x 4.5"	4.5"	1-100W Med. Base **or** 23W CFL
GVR8408K	14.5" H, 8.5" W, 9.5" Ext.	6.5" x 4.5"	5"	1-100W Med. Base **or** 23W CFL
GVR8410K	17.5" H, 10.5" W, 11.5" Ext.	7.5" x 4.5"	5.75"	1-150W Med. Base **or** 40W CFL
GVR9010K	20.5" H, 10.5" W, 10.5" Dp.	-	-	1-150W Med. Base **or** 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Georgetown COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Beveled

CAST *Aluminum*

GT8982IB WET

GT1700IB DAMP

INDOOR OUTDOOR

TITLE 24 WET GT8980IB

WET GT8981IB

WET GT9294IB

Georgetown COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
GT1700IB	17" H, 10" W, 10" Dp.	5.5"	-	3-60W Cand. Base
GT8980IB	13" H, 7.5" W, 9" Ext.	5" x 7.5"	4"	1-150W Med. Base **or** 40W CFL
GT8981IB	18" H, 10" W, 11.5" Ext.	5.25" x 10.5"	8.5"	3-60W Cand. Base
GT8982IB	24" H, 13" W, 15" Ext.	5.75" x 13"	7"	4-60W Cand. Base
GT9294IB	19" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Chimera COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Water

CHI8413IB WET

CAST *Aluminum*

CHI1911IB DAMP TITLE 24

INDOOR OUTDOOR

TITLE 24 WET CHI8407IB

CHI8409IB WET TITLE 24

CHI8411IB WET TITLE 24

TITLE 24 WET CHI9011IB

chimera COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
CHI1911IB	19" H, 11" W, 11" Dp.	5"	-	1-100W Med. Base **or** 23W CFL
CHI8407IB	15.5" H, 7" W, 9.5" Ext.	4.5" x 6.5"	6"	1-100W Med. Base **or** 23W CFL
CHI8409IB	19.5" H, 9" W, 11.5" Ext.	5" x 7.5"	6"	1-100W Med. Base **or** 23W CFL
CHI8411IB	22.5" H, 11" W, 13.5" Ext.	5" x 7.5"	7.5"	1-100W Med. Base **or** 23W CFL
CHI8413IB	28" H, 13" W, 16" Ext.	11" x 7"	11"	4-60W Cand. Base
CHI9011IB	21.5" H, 10.5" W, 10.5" Dp.	-	-	1-100W Med. Base **or** 23W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Milan

FINISH: Mystic Black
SHADE: o pal etched

MLN8309K WET TITLE 24

TITLE 24 WET **MLN8307K**

Milan COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
MLN8307K	14" H, 7" W, 4.5" Ext.	13" x 4.5"	5"	1-100W Med. Base **or** 23W CFL
MLN8309K	16.5" H, 9" W, 5.5" Ext.	15.5" x 5.75"	7"	1-100W Med. Base **or** 23W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Outdoor Lighting

Please see referenced page numbers for larger images and full descriptions of these products.

New England

NA8409PN
See page 119

New England

NA8414PN
See page 119

Zephyr

ZP8414MD
See page 240

Zephyr

ZP8418MD
See page 240

TIFFANY | QUOIZEL

From the **HYACINTH COLLECTION** (p.487)
TF1438VB
Photo courtesy of Enmark Construction Ltd.

Glass color in Tiffany lighting products may vary from images shown. Shade colors will appear darker when not illuminated.

Victory COLLECTION

FINISH:
Valiant Bronze



DAMP TFVY1716VA

NEW!
FOR ◆ 2016

TFVY2819VA DAMP

DAMP TFVY1404VA

All Quoizel Track Lights Swivel

TFVY9359VA

TFVY6325VA

NEW!
FOR ◆ 2016

TFVY6118VA

Enlarged for detail

VictoryCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFVY1404VA	15" H, 43" W, 6" Dp.	6"	4-100W Med. Base **or** 23W CFL	Contains 65 Pieces of Tiffany Glass
TFVY1716VA	13" H, 16" W, 16" Dp.	6"	2-75W Med. Base **or** 18W CFL	Contains 144 Pieces of Tiffany Glass
TFVY2819VA	23.5" H, 19.5" W, 19.5" Dp.	5.25"	3-100W Med. Base **or** 23W CFL	Contains 144 Pieces of Tiffany Glass
TFVY6118VA	19" H, 16" W, 16" Dp.	-	2-75W Med. Base **or** 18W CFL	Contains 192 Pieces of Tiffany Glass
TFVY6325VA	25.5" H, 18" W, 18" Dp.	-	2-100W Med. Base **or** 23W CFL	Contains 192 Pieces of Tiffany Glass
TFVY9359VA	59" H, 18" W, 18" Dp.	-	2-100W Med. Base **or** 23W CFL	Contains 192 Pieces of Tiffany Glass

All chain-hung fixtures come with 8' of wire and 4' of chain.

Alcott COLLECTION

FINISH:
Valiant Bronze

DAMP **TFAT1716VA**

NEW!
FOR ◆ 2016

DAMP **TFAT2821VA**

DAMP **TFAT1507VA**

TFAT9362VA



detail

TFAT6325VA

Enlarged for detail

Alcott COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFAT1507VA	10.5" H*, 7" W, 7" Dp.	2" x 5.5"	1-100W Med. Base **or** 23W CFL	Contains 112 Pieces of Tiffany Glass
TFAT1716VA	15.5" H, 16" W, 16" Dp.	1" x 5.5"	2-100W Med. Base **or** 23W CFL	Contains 240 Pieces of Tiffany Glass
TFAT2821VA	25.5" H, 22" W, 22" Dp.	2.5" x 7.75"	3-100W Med. Base **or** 23W CFL	Contains 320 Pieces of Tiffany Glass
TFAT6325VA	25" H, 19.5" W, 19.5" Dp.	-	2-75W Med. Base **or** 18W CFL	Contains 320 Pieces of Tiffany Glass
TFAT9362VA	62" H, 20.5" W, 20.5" Dp.	-	2-100W Med. Base **or** 23W CFL	Contains 320 Pieces of Tiffany Glass

All chain-hung fixtures come with 8' of wire and 4' of chain. *Comes with (2) 12" and (2) 6" Rods.

Inglenook COLLECTION

FINISH:
Valiant Bronze

DAMP **TFIK1817VA**

DAMP **TFIK2817VA**

TFIK348VA

TFIK1508VA DAMP

Enlarged for detail

TFIK1714VA DAMP

TFIK1404VA DAMP

All Quoizel Track Lights Swivel

Inglenook COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFIK1404VA	14" H, 42" W, 6" Dp.	0.75" x 4.5"	4-100W Med. Base **or** 23W CFL	Each Shade Contains 184 Pieces of Tiffany Glass
TFIK1508VA	7" H*, 8" W, 8" Dp.	5.5"	1-100W Med. Base **or** 23W CFL	Contains 208 Pieces of Tiffany Glass
TFIK1714VA	8" H, 14" W, 14" Dp.	6.5"	2-60W Med. Base **or** 13W CFL	Contains 248 Pieces of Tiffany Glass
TFIK1817VA	12.5" H, 17" W, 17" Dp.	8"	3-100W Med. Base **or** 23W CFL	Contains 248 Pieces of Tiffany Glass
TFIK2817VA	25.5" H, 17.5" W, 17.5" Dp.	7"	3-100W Med. Base **or** 23W CFL	Contains 248 Pieces of Tiffany Glass
TFIK348VA	17.5" H, 47.5" W, 16" Dp	8" x 4.5"	3-100W Med. Base **or** 23W CFL	Contains 496 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.
Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

Inglenook COLLECTION

FINISH:
Valiant Bronze

TFF16191A5VA

TFIK9471VA

TFT16191A1VA

Enlarged for detail

Inglenook COLLECTION

PRODUCT	DIMENSIONS	BULBS	
TFF16191A5VA	62" H, 17" W, 17" Dp.	2-75W Med. Base **or** 18W CFL	Contains 260 Pieces of Tiffany Glass
TFIK9471VA	71" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	Contains 249 Pieces of Tiffany Glass
TFT16191A1VA	25" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 248 Pieces of Tiffany Glass

From the **INGLENOOK COLLECTION:**
TFIK2817VA *(p. 464)*

Inglenook COLLECTION

FINISH:
Valiant Bronze

DAMP **TFIK1617VA**

TFIK8802 DAMP

DAMP **TFIK1509VA**

NEW!
FOR ◆ 2016

TFIK6111VA

Inglenook COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS	
TFIK1509VA	14" H*, 8.5" W, 8.5" Dp.	1.25" x 6"	-	1-100W Med. Base **or** 23W CFL	Contains 37 Pieces of Tiffany Glass
TFIK1617VA	6" H, 16.5" W, 16.5" Dp.	1" x 7"	-	2-75W Med. Base **or** 18W CFL	Contains 253 Pieces of Tiffany Glass
TFIK6111VA	11" H, 8.5" W, 8.5" Dp	-	-	1-60W Med. Base **or** 13W CFL	Contains 37 Pieces of Tiffany Glass
TFIK8802	7" H, 16" W, 5.5" Ext.	-	3"	2-60W Cand. Base	Contains 110 Pieces of Tiffany Glass

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Carroll COLLECTION

FINISH:
Vintage Bronze

DAMP **TF1805SVB**

Enlarged for detail

NEW!
FOR ◆ 2016

DAMP **TF1714VB**

Enlarged for detail

TF1508VB DAMP

Carroll COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1508VB	7" H*, 8" W, 8" Dp.	2.75" x 7"	1-100W Med. Base **or** 23W CFL	Contains 214 Pieces of Tiffany Glass
TF1714VB	16" H, 14.5" W, 14.5" Dp.	6.5"	2-100W Med. Base **or** 23W CFL	Contains 417 Pieces of Tiffany Glass
TF1805SVB	7" H, 17" W, 17" Dp.	7"	2-75W Med. Base **or** 18W CFL	Contains 215 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Asheville COLLECTION

FINISH:
Valiant Bronze

DAMP **TFAS1615VA**

The Asheville Tiffany Collection is a perfect example of understated elegance and class.



TFAS5003VA DAMP

TFAS2817VA DAMP

DAMP TFAS1507VA

DAMP TFAS344VA

Asheville COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFAS1507VA	11.5" H*, 7" W, 7" Dp.	5"	1-100W Med. Base **or** 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS1615VA	6.5" H, 15" W, 15" Dp.	-	2-60W Med. Base **or** 13W CFL	Contains 60 Pieces of Tiffany Glass
TFAS2817VA	23" H, 17" W, 17" Dp.	5"	3-100W Med. Base **or** 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS344VA	29" H, 44" W, 19" Dp.	1" x 4.5"	3-100W Med. Base **or** 23W CFL	Contains 316 Pieces of Tiffany Glass
TFAS5003VA	22.5" H, 23" W, 23" Dp.	5"	3-100W Med. Base **or** 23W CFL	Each Shade Contains 44 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.
Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

Asheville COLLECTION

FINISH:
Valiant Bronze

TFAS1714VA DAMP

TF1180TVA

This Track Light converts to an Island Light

TFAS1404VA DAMP

All Quoizel Track Lights Swivel

Asheville COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1180TVA	25" H, 16" W, 16" Dp.	-	2-75W Med. Base **or** 18W CFL	Contains 44 Pieces of Tiffany Glass
TFAS1404VA	13.5" H*, 43.5" W, 7" Dp.	1.75" x 5.5"	4-100W Med. Base **or** 23W CFL	Each Shade Contains 44 Pieces of Tiffany Glass
TFAS1714VA	12" H, 14" W, 14" Dp	5.5"	2-100W Med. Base **or** 23W CFL	Contains 44 Pieces of Tiffany Glass

*Comes with (2) 6" and (2) 12" Rods.

From the **ASHEVILLE COLLECTION:**
TF1180TVA

Asheville COLLECTION

FINISH:
Valiant Bronze

NEW!
FOR ◆ 2016

DAMP **TFAS1817VA**

TFAS9360VA

TFAS9470VA

NEW!
FOR ◆ 2016

Asheville COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFAS1817VA	17.5" H, 17" W, 17" Dp.	5.5"	3-100W Med. Base **or** 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS9360VA	60" H, 17" W, 17" Dp.	-	2-100W Med. Base **or** 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS9470VA	70.5" H, 12" W, 12" Dp.	-	1-150W Med. Base **or** 40W CFL	Contains 52 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

Larissa COLLECTION

TF879T

TF879F

Larissa COLLECTION

PRODUCT	DIMENSIONS	BULBS	
TF879F	62" H, 18" W, 18" Dp.	2-100W Med. Base **or** 23W CFL	Contains 426 Pieces of Tiffany Glass
TF879T	22.5" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 426 Pieces of Tiffany Glass

Kami COLLECTION

FINISH:
Vintage Bronze

DAMP **TFKM5103VB**

TFKM2840VB

TFKM1508VB

TF878CVB

kamiCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF878CVB†	10.5" H, 20" W, 20" Dp.	5.5"	3-100W Med. Base **or** 23W CFL	Contains 360 Pieces of Tiffany Glass
TFKM1508VB	8.5" H*, 8" W, 8" Dp.	5.5"	1-100W Med. Base **or** 23W CFL	Contains 159 Pieces of Tiffany Glass
TFKM2840VB††	33.5" H, 40" W, 40" Dp.	5.25"	8-100W Med. Base **or** 23W CFL	Contains 532 Pieces of Tiffany Glass
TFKM5103VB†	22.5" H, 24.5" W, 24.5" Dp.	5.125"	3-100W Med. Base **or** 23W CFL	Each Shade Contains 159 Pieces of Tiffany Glass

†Chain-hung fixtures come with 8' of wire and 4' of chain. ††Chain-hung fixture comes with 12' of wire and 8' of chain. Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

Kami COLLECTION

FINISH:
VB Vintage Bronze

DAMP **TF1396SVB**

TF878T

Enlarged for detail

TF878F

TF878UVB

Kami COLLECTION

PRODUCT	DIMENSIONS	BULBS	
TF1396SVB	6" H, 17" W, 17" Dp.	2-75W Med. Base **or** 18W CFL	Contains 367 Pieces of Tiffany Glass
TF878F	62" H, 18" W, 18" Dp.	2-100W Med. Base **or** 23W CFL	Contains 366 Pieces of Tiffany Glass
TF878T	23" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 366 Pieces of Tiffany Glass
TF878UVB	70" H, 14" W, 14" Dp.	1-150W Med. Base **or** 40W CFL	Contains 366 Pieces of Tiffany Glass

Stephen COLLECTION

FINISH:
Vintage Bronze

TFST2822VB DAMP

TFST2840VB 50 DAMP

DAMP TFST5103VB

DAMP TF885SVB

Stephen COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFST2822VB*	27.5" H, 21.5" W, 21.5" Dp.	7"	4-100W Med. Base **or** 23W CFL	Contains 368 Pieces of Tiffany Glass
TFST2840VB**	43" H, 40" W, 40" Dp.	7.75"	8-100W Med. Base **or** 23W CFL	Contains 615 Pieces of Tiffany Glass
TFST5103VB*	19.5" H, 24" W, 24" Dp.	5.125"	3-100W Med. Base **or** 23W CFL	Each Shade Contains 152 Pieces of Tiffany Glass
TF885SVB	14.5" H, 14" W, 14" Dp.	6.5"	2-100W Med. Base **or** 23W CFL	Contains 248 Pieces of Tiffany Glass

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Chain-hung fixture comes with 12' of wire and 8' of chain.

Stephen COLLECTION

FINISH:
Vintage Bronze

TFST8701VB

TF885F

TFST1508VB



TF1018TVB

Stephen COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	
TF885F	59.5" H, 18" W, 18" Dp.	-	-	2-100W Med. Base **or** 23W CFL	Contains 256 Pieces of Tiffany Glass
TF885T	23" H, 16" W, 16" Dp.	-	-	2-75W Med. Base **or** 18W CFL	Contains 248 Pieces of Tiffany Glass
TF1018TVB	12" H, 5" W, 5" Dp.	-	-	1-25W Cand. Base	Contains 124 Pieces of Tiffany Glass
TFST1508VB	6" H*, 8" W, 8" Dp.	5.5"	-	1-100W Med. Base **or** 23W CFL	Contains 152 Pieces of Tiffany Glass
TFST8701VB	10" H, 8" W, 10.5" Dp.	5" x 5"	7.5"	1-100W Med. Base **or** 23W CFL	Contains 152 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

From the **STEPHEN COLLECTION:**
TF885T

Monteclaire COLLECTION

FINISH: Western Bronze
GLASS: tiffany & Mica

QUOIZEL NATURALS MICA

TFMC1818WT DAMP

PULL CHAIN

TFMC2818WT DAMP

NEW!
FOR ◆ 2016

TFMC1715WT DAMP

TFMC1508WT DAMP



detail

Monteclaire COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFMC1508WT	8" H*, 7.5" W, 7.5" Dp.	5"	1-60W Med. Base **or** 13W CFL	Contains 236 Pieces of Tiffany & Mica Glass
TFMC1715WT	13" H, 15" W, 15" Dp.	6"	2-60W Med. Base **or** 13W CFL	Contains 252 Pieces of Tiffany & Mica Glass
TFMC1818WT	10" H, 18" W, 18" Dp.	5"	3-60W Med. Base **or** 13W CFL	Contains 252 Pieces of Tiffany & Mica Glass
TFMC2818WT	22" H, 18" W, 18" Dp.	5"	3-60W Med. Base **or** 13W CFL	Contains 252 Pieces of Tiffany & Mica Glass

All chain-hung fixtures come with 8' of wire and 4' of chain. All rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

BelleFleur COLLECTION

FINISH:
Vintage Bronze

DAMP **TFBF348VB**

TFBF9362VB

DAMP **TF1781VB**

BelleFleur COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1781VB	28" H, 23" W, 23" Dp.	6"	4-100W Med. Base **or** 23W CFL	Contains 608 Pieces of Tiffany Glass
TFBF348VB	18" H, 48" W, 16" Dp.	8" x 4.5"	3-100W Med. Base **or** 23W CFL	Contains 884 Pieces of Tiffany Glass
TFBF9362VB	62" H, 20" W, 20" Dp.	-	3-100W Med. Base **or** 23W CFL	Contains 532 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

From the **WEST END COLLECTION:**
TF1541VB

WestEnd COLLECTION

FINISH:
VB Vintage Bronze **BB** Brushed Bullion

TF1541VB

TF9320BB

PULL CHAIN

TF1400SVB

TF6660BB

WestEnd COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1400SVB	6" H, 17" W, 17" Dp.	-	2-75W Med. Base **or** 18W CFL	Contains 262 Pieces of Tiffany Glass
TF1541VB	8.5" H*, 6" W, 6" Dp.	5"	1-100W Med. Base **or** 23W CFL	Contains 153 Pieces of Tiffany Glass
TF6660BB	26.5" H, 16" W, 16" Dp.	-	2-75W Med. Base **or** 18W CFL	Contains 306 Pieces of Tiffany Glass
TF9320BB	60" H, 18" W, 18" Dp.	-	2-100W Med. Base **or** 23W CFL	Contains 306 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

TF1791TWT

Pomeroy

FINISH: Western Bronze

TF9397VB

TF6668VB

Gotham

FINISH: Vintage Bronze

PRODUCT	DIMENSIONS	BULBS	
TF1791TWT	21" H, 13" W, 15" Dp.	1-75W Med. Base **or** 18W CFL	Contains 4 Pieces of Tiffany Glass Panels
TF6668VB	24.5" H, 19" W, 19" Dp.	2-75W Med. Base **or** 18W CFL	Contains 48 Pieces of Tiffany Glass
TF9397VB	62" H, 20.5" W, 20.5" Dp.	2-100W Med. Base **or** 23W CFL	Contains 64 Pieces of Tiffany Glass

Hyacinth COLLECTION

FINISH:
Vintage Bronze

DAMP **TF1737VB**

DAMP **TF1618VB**

The Hyacinth Tiffany glass design is one of our prettiest and most vibrant. Watch it add color and style to your home décor!

DAMP **TF1438VB**

DAMP **TF1536VB**

Hyacinth COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1438VB†	26.5" H, 22" W, 22" Dp.	5"	3-100W Med. Base **or** 23W CFL	Contains 540 Pieces of Tiffany Glass
TF1536VB	8.5" H*, 9" W, 9" Dp.	5.5"	1-100W Med. Base **or** 23W CFL	Contains 188 Pieces of Tiffany Glass
TF1618VB†	15" H, 22" W, 22" Dp.	6.25"	3-100W Med. Base **or** 23W CFL	Contains 540 Pieces of Tiffany Glass
TF1737VB††	11.5" H, 12.5" W, 12.5" Dp.	6.25"	1-150W Med. Base **or** 40W CFL	Contains 295 Pieces of Tiffany Glass

Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods. †Chain-hung fixtures come with 8' of wire and 4' of chain.
††Fixture comes with 12' of wire and 8' of chain.

INTEGRATED LED
10 YEAR WARRANTY

TF1860FZ

TF7110ZLED

Pueblo
FINISH: Medici Bronze

TF9152ZLED

TF1860TZ

Montgomery
FINISH: Medici Bronze

LED CHART

TF7110ZLED / TF9152ZLED / TF1860TZ TF1860FZ	
Lumens	519
Total Watts	5W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3117K
Dimmable	No

PRODUCT	DIMENSIONS	LIGHT SOURCE	
TF1860FZ	51" H, 22.5" W, 9" Dp.	See LED Chart	Contains 40 Pieces of Tiffany Glass
TF1860TZ	19" H, 19" W, 6" Dp.	See LED Chart	Contains 40 Pieces of Tiffany Glass
TF7110ZLED	19" H, 19" W, 6" Dp.	See LED Chart	Contains 42 Pieces of Tiffany Glass
TF9152ZLED	51" H, 22.5" W, 9" Dp.	See LED Chart	Contains 42 Pieces of Tiffany Glass

From the **PUEBLO COLLECTION:**
TF7110ZLED

Jewel DRAGONFLY

FINISH: Malaga

DAMP TFJD2836ML

DAMP TFJD2822ML

Dragonfly Tiffanys are particularly intricate in their handcrafted artistry.

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFJD2822ML*	24" H, 22" W, 22" Dp.	5"	4-100W Med. Base **or** 23W CFL	Contains 315 Pieces of Tiffany Glass
TFJD2836ML**	36.5" H, 35.5" W, 35.5" Dp.	5"	6-100W Med. Base **or** 23W CFL	Contains 540 Pieces of Tiffany Glass

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Chain-hung fixture comes with 12' of wire and 8' of chain.

TF1508FVB

King

FINISH: Vintage Bronze



TF1508TVB

Enlarged for detail

Copperfly

FINISH: Imperial Bronze

TF1851TIB

PRODUCT	DIMENSIONS	BULBS	
TF1508FVB	62" H, 18" W, 18" Dp.	2-100W Med. Base **or** 23W CFL	Contains 318 Pieces of Tiffany Glass
TF1508TVB	24" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 318 Pieces of Tiffany Glass
TF1851TIB	16.5" H, 17" W, 17" Dp.	2-75W Med. Base **or** 18W CFL	Contains 324 Pieces of Tiffany Glass



Arden

TF1135T

Enlarged for detail

TF1135F

TF1672TWT

Revere

FINISH: Western Bronze

PRODUCT	DIMENSIONS	BULBS	
TF1135F	59.5" H, 18" W, 18" Dp.	2-100W Med. Base **or** 23W CFL	Contains 192 Pieces of Tiffany Glass
TF1135T	23.5" H, 16" W, 16" Dp.	2-60W Med. Base **or** 13W CFL	Contains 192 Pieces of Tiffany Glass
TF1672TWT	22" H, 14" W, 14" Dp.	2-60W Med. Base **or** 13W CFL	Contains 196 Pieces of Tiffany Glass

Tiffany ANIMALS

TFX1520T

AngelFISH

Contains 39 Pieces of Tiffany Glass

FlowerTURTLE

TFX1519T

Contains 111 Pieces of Tiffany Glass

GreenFROG

TFX837Y

Contains 104 Pieces of Tiffany Glass

TF6031VB

Flowered LADYBUG

FINISH: Vintage Bronze

Contains 62 Pieces of Tiffany Glass

RainbowBUTTERFLY

TFX1518T

Contains 59 Pieces of Tiffany Glass



TF6033VB

LoungingFROG

FINISH: Vintage Bronze

Contains 55 Pieces of Tiffany Glass and 4 jewels

TF6599R

OrangeBUTTERFLY

FINISH: Architectural Bronze

Contains 84 Pieces of Tiffany Glass



PRODUCT	DIMENSIONS	BULBS
TF6031VB	4" H, 7" W, 6" Dp.	1-15W T7 Cand. Base Supplied
TF6033VB	3.5" H, 8" W, 7" Dp.	1-15W T7 Cand. Base Supplied
TF6599R	9" H, 6" W, 7.5" Dp.	1-15W T7 Cand. Base Supplied
TFX1518T	9" H, 5" W, 5" Dp.	1-15W T7 Cand. Base Supplied
TFX1519T	3.5" H, 5.5" W, 8" Dp.	1-15W T7 Cand. Base Supplied
TFX1520T	6" H, 3" W, 2" Dp.	1-15W T7 Cand. Base Supplied
TFX837Y	6" H, 8.5" W, 9" Dp.	1-15W T7 Cand. Base Supplied

Purple WISTERIA

TF1139T

TF6034R

Laburnum

FINISH: Architectural Bronze

Lynch

TF1487T

PRODUCT	DIMENSIONS	BULBS	
TF1139T	19.5" H, 10.5" W, 10.5" Dp.	1-60W Med. Base **or** 13W CFL	Contains 479 Pieces of Tiffany Glass
TF1487T	26" H, 15.5" W, 15.5" Dp.	2-75W Med. Base **or** 18W CFL	Contains 371 Pieces of Tiffany Glass
TF6034R	31" H, 22" W, 22" Dp.	3-100W Med. Base **or** 23W CFL	Contains 1998 Pieces of Tiffany Glass

Mariah

FINISH: Vintage Bronze

TFMH1820VB DAMP

PULL CHAIN

TF1575TIB

LED LIGHT

Berkshire

FINISH: Imperial Bronze

TF1850TIB

Jewel

FINISH: Imperial Bronze

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1575TIB	27.5" H, 16" W, 16" Dp.	-	2-75W Med. Base **or** 18W CFL +1-1W LED (Supplied)	Contains 363 Pieces of Tiffany Glass
TF1850TIB	23.5" H, 16" W, 16" Dp.	-	2-75W Med. Base **or** 18W CFL	Contains 297 Pieces of Tiffany Glass
TFMH1820VB	12" H, 20" W, 20" Dp.	7"	3-100W Med. Base **or** 23W CFL	Contains 336 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

Alahambre

FINISH: Vintage Bronze

TF1816VB

TF1408SVB DAMP

Reed

FINISH: Vintage Bronze

Graham

FINISH: Vintage Bronze

TF1409SVB DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1408SVB	6" H, 17" W, 17" Dp.	1" x 7"	2-75W Med. Base **or** 18W CFL	Contains 308 Pieces of Tiffany Glass
TF1409SVB	6" H, 17" W, 17" Dp.	1" x 7"	2-75W Med. Base **or** 18W CFL	Contains 186 Pieces of Tiffany Glass
TF1816VB	25" H, 22" W, 22" Dp.	5.5"	4-100W Med. Base **or** 23W CFL	Contains 128 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

Indus

FINISH: Vintage Bronze



TF6669VB

TF9404M

GrovePark

FINISH: Multi

GEOMETRIC IRON ACCENTS

TF6898M

PRODUCT	DIMENSIONS	BULBS	
TF6669VB	23" H, 16" W, 16" Dp.	2-60W Med. Base **or** 13W CFL	Contains 105 Pieces of Tiffany Glass
TF6898M	23.5" H, 14" W, 14" Dp.	2-60W Med. Base **or** 13W CFL	Contains 240 Pieces of Tiffany Glass
TF9404M	60" H, 17" W, 17" Dp.	2-100W Med. Base **or** 23W CFL	Contains 240 Pieces of Tiffany Glass

Lucia

TF1868T

TF1873T

QueensMeadow

TF6826VB

Connie

FINISH: Vintage Bronze

PRODUCT	DIMENSIONS	BULBS	
TF1868T	24.5" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 690 Pieces of Tiffany Glass
TF1873T	23.5" H, 20" W, 20" Dp.	2-75W Med. Base **or** 18W CFL	Contains 498 Pieces of Tiffany Glass
TF6826VB	22" H, 14" W, 14" Dp	2-60W Med. Base **or** 13W CFL	Contains 387 Pieces of Tiffany Glass

TF1901VB

Adriana

FINISH: Vintage Bronze

detail

Florentine

FINISH: Vintage Bronze

TF1784VB

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1784VB	39" H, 40" W, 40" Dp.	5.5"	8-100W Med. Base **or** 23W CFL	Contains 2331 Pieces of Tiffany Glass
TF1901VB	28" H, 32" W, 32" Dp.	5.5"	6-100W Med. Base **or** 23W CFL	Contains 515 Pieces of Tiffany Glass

All chain-hung fixtures come with 12' of wire and 8' of chain.

NEW!
FOR ◆ 2016

TF2076TVB

Enlarged for detail

Lance

FINISH: Vintage Bronze



TF2076FVB



TF1433T

Pearson

PRODUCT	DIMENSIONS	BULBS	
TF1433T	23" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 240 Pieces of Tiffany Glass
TF2076FVB	60" H, 20" W, 20" Dp.	2-100W Med. Base **or** 23W CFL	Contains 195 Pieces of Tiffany Glass
TF2076TVB	25" H, 19.5" W, 19.5" Dp.	2-75W Med. Base **or** 18W CFL	Contains 180 Pieces of Tiffany Glass

Ava

FINISH: Vintage Bronze

TFAV1714VB DAMP

TF489T

DAMP **TF489P01VB**

Chastain

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF489T	22.5" H, 15.5" W, 15.5" Dp.	-	2-60W Med. Base **or** 13W CFL	Contains 140 Pieces of Tiffany Glass
TF489P01VB	14" H*, 5" W, 5" Dp.	5.5"	1-100W Med. Base **or** 23W CFL	Contains 51 Pieces of Tiffany Glass
TFAV1714VB	9" H, 14" W, 14" Dp.	1.5" x 11"	2-60W Med. Base **or** 13W CFL	Contains 342 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" rods.

Bryant

TF1427T

TF1427F

TF1021TVB

Holmes

FINISH: Vintage Bronze

PRODUCT	DIMENSIONS	BULBS	
TF1021TVB	12" H, 5" W, 5" Dp.	1-25W Cand. Base	Contains 84 Pieces of Tiffany Glass
TF1427F	60" H, 17" W, 17" Dp.	2-100W Med. Base **or** 23W CFL	Contains 112 Pieces of Tiffany Glass
TF1427T	23" H, 14" W, 14" Dp.	2-75W Med. Base **or** 18W CFL	Contains 112 Pieces of Tiffany Glass

Bragg Creek

FINISH: Russet

TF1916TRS

Navajo

FINISH: Valiant Bronze

TFNO6325VA

NEW!
FOR ◆ 2016

TF2095TRS

Gibbons

FINISH: Russet

PRODUCT	DIMENSIONS	BULBS	
TF1916TRS	24.5" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18 CFL	Contains 72 Pieces of Tiffany Glass
TF2095TRS	22.5" H, 14" W, 14" Dp.	2-75W Med. Base **or** 18W CFL	Contains 172 Pieces of Tiffany Glass
TFNO6325VA	25" H, 15" W, 15" Dp.	2-75W Med. Base **or** 18W CFL	Contains 292 Pieces of Tiffany Glass

Palmetto

FINISH: Imperial Bronze

TF1848TIB

Fields

FINISH: Western Bronze



TF1425TWT

Cambridge

FINISH: Vintage Bronze

TFCB6325VB

PRODUCT	DIMENSIONS	BULBS	
TF1425TWT	24" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 330 Pieces of Tiffany Glass
TF1848TIB	26.5" H, 18" W, 18" Dp.	2-75W Med. Base **or** 18W CFL	Contains 186 Pieces of Tiffany Glass
TFCB6325VB	23.5" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 318 Pieces of Tiffany Glass

Viking

FINISH: Vintage Bronze

TF1917TVA

India

FINISH: Imperial Bronze

TF1846TIB

TF1913TRS

Jewel Heart

FINISH: Russet

PRODUCT	DIMENSIONS	BULBS	
TF1846TIB	19.5" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 282 Pieces of Tiffany Glass
TF1913TRS	23" H, 14" W, 14" Dp.	2-60W Med. Base **or** 13W CFL	Contains 224 Pieces of Tiffany Glass
TF1917TVA	25.5" H, 16" W, 16" Dp.	2-75W Med. Base **or** 18W CFL	Contains 260 Pieces of Tiffany Glass

TF1783CIB DAMP

Lennon

FINISH: Imperial Bronze

Kelso

NEW!
FOR ◆ 2016

TF2041T

TFCC8802

Classic Craftsman

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS	
TF1783CIB	17.5" H, 16" W, 16" Dp.	5"	-	4-60W Cand. Base	Contains 24 Pieces of Tiffany Glass
TF2041T	24" H, 15" W, 15" Dp.	-	-	2-75W Med. Base **or** 18W CFL	Contains 52 Pieces of Tiffany Glass
TFCC8802	7" H, 16.5" W, 5.5" Ext	-	2.5	2-60W Cand. Base	Contains 116 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

From the **STOCKTON COLLECTION:**
Q1056FPN *(p. 514)*

Please see our Portables Catalog (CQP3017X) for an exclusive presentation of portable products and mirrors.

Kingsley COLLECTION

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze

SHADE: **BN** White Hardback Fabric with Double Trim
PN Cream Hardback Fabric Shade with Double Trim

NEW!
FOR ◆ 2016

VVKY9658BN

VVKY9658PN

VVKY9258BN

VVKY9258PN

VVKY9558BN

VVKY9558PN

VIVID
The Brighter Light

VIVID The Brighter Light LED

VIVID provides **3 times the light output** of single socket lamps.

Our ViViD 3-Light Cluster features:

- Easy Turn Switch
- 3 Light levels
- Your choice:
  Edison bulbs, Retro-Fit Fluorescent Bulbs, or Retro-Fit LED bulbs



VVKY9358BN



VVKY9358PN

VVKY6328PN

Enlarged for detail

VVKY6328BN

NEW!
FOR ◆ 2016

Kingsley COLLECTION

PRODUCT	DIMENSIONS	BULBS	SHADE
VVKY6328BN/PN	28" H, 15" W, 15" Dp.	3-75W Med. Base **or** 18W CFL	(10" x 12") x (12" x 15") x 15"
VVKY9258BN/PN	58" H, 16" W, 16" Dp.	3-75W Med. Base **or** 18W CFL	(10" x 13") x (13" x 16") x 16"
VVKY9358BN/PN	61" H, 16" W, 16" Dp.	3-75W Med. Base **or** 18W CFL	(10" x 13") x (13" x 16") x 16"
VVKY9558BN/PN	58" H, 16" W, 16" Dp.	3-75W Med. Base **or** 18W CFL	(10" x 13") x (13" x 16") x 16"
VVKY9658BN/PN	58" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL + 3-75W Med. Base **or** 18W CFL	(10" x 13") x (13" x 16") x 16"

INTEGRATED LED
10 YEAR WARRANTY

VVBT6220WT

Enlarged for detail

VVBT9348WT

Benedict

FINISH: Western Bronze
GLASS: Frosted

NEW!
FOR ◆ 2016

LED CHART

VVBT6220WT / VVBT9348WT

Lumens	507
Total Watts	5W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3053K
Dimmable	Yes

VIVID
The Brighter Light

CLEAR GLASS ACCENT

VVCS6332OI

VVCS9556OI

Cruise

FINISH: Oil Rubbed Bronze
SHADE: Cream Linen Hardback Fabric with Self Trim Top and Bottom

VVCS9360OI

PRODUCT	DIMENSIONS	BULBS/LIGHT SOURCE	SHADE DIMS.
VVBT6220WT	20" H, 17" W, 8" Dp.	See LED chart	-
VVBT9348WT	48" H, 20.5" W, 11" Dp.	See LED chart	-
VVCS6332OI	32.5" H, 15" W, 15" Dp.	3-75W Med. Base **or** 18W CFL	10" x 12" x 15"
VVCS9360OI	58.5" H, 15" W, 15" Dp.	3-75W Med. Base **or** 18W CFL	10" x 12" x 15"
VVCS9556OI	55.5" H, 15" W, 15" Dp.	3-75W Med. Base **or** 18W CFL	10" x 12" x 15"

Ambrose

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
SHADE: Geneva White Hardback Fabric

VVAM9362BN

Enlarged for detail

VVAM9362PN

VVAM6130PN

Enlarged for detail

VVAM6130BN

QUOIZEL NATURALS MICA

Whitney

FINISH: imperial Bronze

INTEGRATED LED
10 YEAR WARRANTY

VVWH9348IB

VIVID
The Brighter Light

LED CHART

VVWH9348IB

Lumens	507
Total Watts	5W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3053K
Dimmable	Yes

PRODUCT	DIMENSIONS	BULBS/LIGHT SOURCE	SHADE DIMS.
VVAM6130BN/PN	30.5" H, 15" W, 15" Dp.	3-75W Med. Base **or** 18W CFL	15" x 15" x 10"
VVAM9362BN/PN	62.5" H, 17" W, 17" Dp.	3-75W Med. Base **or** 18W CFL	15" x 15" x 10"
VVWH9348IB	49" H, 20.5" W, 11" Dp.	See LED chart	-

VIVID
The Brighter Light

Spencer

FINISH: **BN** Brushed Nickel
WT Western Bronze

VVSP9348WT

VVSP9348BN

VVTH9348AB

INTEGRATED **LED**
10 YEAR WARRANTY

VVTH9348IB

Thompson

FINISH: **AB** Aged Brass
IB imperial Bronze

LED CHART

VVTH9348AB/IB / VVSP9348BN/WT

Lumens	645
Total Watts	7W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3054K
Dimmable	Yes

PRODUCT	DIMENSIONS	LIGHT SOURCE
VVSP9348BN/WT	47.5" H, 21" W, 11" Dp.	See LED chart
VVTH9348AB/IB	49" H, 21" W, 11" Dp.	See LED chart

Buckler

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
SHADE: Off-White Hardback Fabric

Q1632TPN

Enlarged for detail

OPTIC GLASS

Q1633FBN

Q1634TPN

Q1634TBN

Q1634FPN

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1632TPN	24" H, 12" W, 12" Dp.	1-100W Med. Base **or** 23W CFL	8" x 12" x 12"
Q1634TBN/TPN	29.5" H, 15" W, 15" Dp.	1-150W Med. Base **or** 40W CFL	11" x 13" x 15"
Q1633FBN	60" H, 15" W, 15" Dp.	1-100W Med. Base **or** 23W CFL	10" x 13" x 15"
Q1634FPN	60" H, 15" W, 15" Dp.	1-100W Med. Base **or** 23W CFL	10" x 13" x 15"

Stockton

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
SHADE: **BN** White Softback **PN** Cream Softback

Q1054FBN

Q1054FPN

Q1056FBN

Q1056FPN

Q1054TBN

Enlarged for detail

Q1054TPN

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1054FBN/FPN	60" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	11" x 9" x 16"
Q1054TBN/TPN	27" H, 15" W, 15" Dp.	1-100W Med. Base **or** 23W CFL	10.5" x 8" x 15"
Q1056FBN/FPN	61" H, 15" W, 15" Dp.	1-100W Med. Base **or** 23W CFL	11" x 7" x 15"

Q1055FBN

Stockton

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
SHADE: **BN** White Softback **PN** Cream Softback

Q1055FPN

Q1073FPN

Q1072FPN

Q1072TPN

Archer

FINISH: Palladian Bronze
SHADE: Cream Softback Fabric

Q1074FPN

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1055FBN/FPN	60.5" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	11" x 9" x 16"
Q1072FPN	60.5" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	11" x 9" x 16"
Q1072TPN	26" H, 15" W, 15" Dp.	1-100W Med. Base **or** 23W CFL	10.5" x 8" x 15"
Q1073FPN	59.5" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	11" x 9" x 16"
Q1074FPN	61" H, 15" W, 15" Dp.	1-100W Med. Base **or** 23W CFL	11" x 7" x 15"

Humphrey

FINISH: **AB** Aged Brass
PN Palladian Bronze

Q1919TPN

Q1919TAB

Enlarged for detail

Q1918TPN

Enlarged for detail

Q1918TBN

Innovation

FINISH: **BN** Brushed Nickel
PN Palladian Bronze

INTEGRATED LED
10 YEAR WARRANTY

Jensen

FINISH: **AB** Aged Brass
BN Brushed Nickel

Q1852TAB

Q1852TBN

Enlarged for detail

LED CHART

	Q1852TAB/TBN	Q1918TBN/TPN	Q1919TAB/TPN
Lumens	507	360	360
Total Watts	5W	5W	5W
Color Rendering Index (CRI)	82	80	80
Color Temperature (CCT)	3053K	3000K	3000K
Dimmable	Yes	Yes	Yes

PRODUCT	DIMENSIONS	LIGHT SOURCE
Q1852TAB/TBN	20.5" H, 21.5" W, 6.5" Dp.	See LED chart
Q1918TBN/TPN	14" H, 5.5" W, 5.5" Dp.	See LED chart
Q1919TAB/TPN	14" H, 4.5" W, 4.5" Dp.	See LED chart

SUNSET BRASS ACCENTS

Q1889FOI

Haskell

FINISH: Oil Rubbed Bronze

Q1892FOI

Lyndhurst

FINISH: Oil Rubbed Bronze
SHADE: Tan Linen Hardback Fabric

HI-LO OFF SWITCH

Q1914T

Weaving

SHADE: White Linen Hardback

OPTIC CRYSTAL

Q1893FOI

Bray

SHADE: Grey Softback

Q1915T

Jenkins

FINISH: Oil Rubbed Bronze
SHADE: Cream Linen Hardback

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1889FOI	54.5" H, 18" W, 10" Dp.	1-60W Med. Base **or** 13W CFL	-
Q1892FOI	58.5" H, 14" W, 14" Dp.	1-150W Med. Base **or** 40W CFL	7.5" x 13" x 14"
Q1893FOI	56.5" H, 21" W, 14" Dp.	1-75W Med. Base **or** 18W CFL + 1-7W Cand. Base	7.5" x 12" x 14"
Q1914T	26" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	10" x 15" x 16"
Q1915T	27.5" H, 18" W, 12.5" Dp.	1-150W Med. Base **or** 40W CFL	(12" x 16") x (9" x 18") x 12.5"

INTEGRATED LED
10 YEAR WARRANTY

Marx

FINISH: **BN** Brushed Nickel
WT Western Bronze

Q2125TWT

Q2125TBN

Enlarged for detail

NEW!
FOR ◆ 2016

Sway

FINISH: **T** Painted Blue Gray Combo
T1 Black Combo

Q2313T

Enlarged for detail

Q2313T1

Q2312T

Enlarged for detail

Q2312T1

LED CHART

	Q2312T/T1 / Q2313T/T1	Q2125TBN/WT
Lumens	300	450
Total Watts	3W	2.5W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	No	Yes

Encore

FINISH: **T** Black Combo
T1 Gray Combo

PRODUCT	DIMENSIONS	LIGHT SOURCE
Q2125TBN/TWT	19" H, 15" W, 7.5" Dp.	See LED chart
Q2312T/T1	18" H, 6" W, 2.5" Dp.	See LED chart
Q2313T/T1	16" H, 8" W, 7" Dp.	See LED chart

Q2310F1

Westway

FINISH: **F** Painted Antique Gray
F1 Black Combo

NEW!
FOR ◆ 2016

Q2310F

Enlarged for detail

Studio

FINISH: **T** Painted Gray
T1 Black Combo

Q2311T1

Enlarged for detail

Q2311T

Q2126FWT

Enlarged for detail

Blaine

FINISH: Western Bronze

Q2126TWT

PRODUCT	DIMENSIONS	BULBS
Q2126FWT	57" H, 18" W, 11" Dp.	1-100W Med. Base **or** 23W CFL
Q2126TWT	25" H, 13" W, 8" Dp.	1-100W Med. Base **or** 23W CFL
Q2310F/F1	49" H, 20" W, 11.5" Dp.	1-60W Med. Base **or** 13W CFL
Q2311T/T1	12" H, 7" W, 7" Dp.	1-60W Cand. Base

Q2314T

Ocean

SHADE: White Fabric

Slade

FINISH: Western Bronze
SHADE: Cream Hardback

Q2127TWT

NEW!
FOR ◆ 2016

Blue River

SHADE: White Linen Fabric

Q2315T

Q2316T1

Q2316T

Dune

SHADE: **T** White Fabric
T1 Gold Fabric

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q2127TWT	33" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	(11" x 14") x (14" x 16") x 16"
Q2314T	35" H, 17" W, 17" Dp.	2-60W Med. Base **or** 13W CFL	(10" x 15") x (15" x 17") x 17"
Q2315T	27.5" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	(10" x 14") x (14" x 16") x 16"
Q2316T/T1	22.5" H, 15" W, 15" Dp.	1-150W Med. Base **or** 40W CFL	(10" x 13") x (13" x 15") x 15"

Looping
SHADE: Gold Fabric

Q2320T

Sable
SHADE: White Fabric

Q2317T

NEW!
FOR ◆ 2016

Starling
SHADE: Gold Fabric

Q2319T

Q2321T

Percy
SHADE: Gold Fabric

Q2318T

Aquatic
SHADE: White Fabric

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q2317T	25.5" H, 14" W, 14" Dp.	1-100W Med. Base **or** 23W CFL	(9.5" x 12") x (12" x 14") x 14"
Q2318T	28.5" H, 15" W, 15" Dp.	2-60W Med. Base **or** 13W CFL	8" x 14.5" x 14.5"
Q2319T	30" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	(10" x 14") x (14" x 16") x 16"
Q2320T	29.5" H, 18" W, 18" Dp.	1-150W Med. Base **or** 40W CFL	10.5" x 18" x 18"
Q2321T	27" H, 17" W, 17" Dp.	1-150W Med. Base **or** 40W CFL	(11" x 15") x (15" x 17") x 17"

Barrel

SHADE: Gold Fabric

NEW!
FOR ◆ 2016

Q2322T

Q2324T

NEW!
FOR ◆ 2016

Seaside

SHADE: White Fabric

Q1630FPN

Sandy

SHADE: Gold Fabric

Q2323T

NEW!
FOR ◆ 2016

Abbey

FINISH: PalladianBronze
SHADE: Pleated Fabric

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1630FPN	59" H, 15" W, 15" Dp.	1-100W Med. Base **or** 23W	10" x 11" x 15"
Q2322T	29" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	10" x 16" x 16"
Q2323T	30" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	(10" x 14") x (14" x 16") x 16"
Q2324T	29" H, 17" W, 17" Dp.	1-150W Med. Base **or** 40W CFL	(11" x 15") x (15" x 17") x 17"

Garnet

SHADE: White Linen Fabric

Q2325T

NEW!
FOR ◆ 2016

SL702G
SL701G

SL703G

SatinLace

FINISH: French Gold Flemish

AB703A

AB701A
AB702A

AbigailAdams

FINISH: Antique Brass

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
AB701A	20" H, 8.5" W, 8.5" Dp.	1-75W Med. Base **or** 18W CFL + 1-7W C7 Cand. Base*	-
AB702A	24" H, 11" W, 11" Dp.	1-150W Med. Base **or** 40W CFL + 1-7W C7 Cand. Base*	-
AB703A	28" H, 14" W, 14" Dp.	1-150W Med. Base **or** 40W CFL + 1-7W C7 Cand. Base*	-
Q2325T	30" H, 16" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	(10" x 14") x (14" x 16") x 16"
SL701G	20" H, 8" W, 8" Dp.	1-75W Med. Base **or** 18W CFL + 1-7W C7 Cand. Base*	-
SL702G	24" H, 10" W, 10" Dp.	1-150W Med. Base **or** 40W CFL + 1-7W C7 Cand. Base*	-
SL703G	28" H, 12.5" W, 12.5" Dp.	1-150W Med. Base **or** 40W CFL + 1-7W C7 Cand. Base*	-

Q1295KPK

Linear

INTEGRATED LED
10 YEAR WARRANTY

FINISH: Polished Nickel



Q4571A

Beckett

SHADE: Beige Linen Drum

LED CHART

	Q1295KPK
Lumens	507
Total Watts	5W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3053K
Dimmable	YES

QJF15078BTR

QJ6781TR

QM6904M

Glenhaven

FINISH: Teco Rossa
GLASS: Amber Etched

String Shade

FINISH: Combo
SHADE: Natural String

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1295KPK	28" H, 27.5" W, 27.5" Dp.	See LED chart	-
Q4571A	72.5" H, 53" W, 16" Dp.	1-150W Med. Base **or** 40W CFL	16" x 17"
QJ6781TR	18" H, 14" W, 14" Dp.	2-60W Med. Base **or** 13W CFL	-
QJF15078BTR	60.5" H, 18" W, 18" Dp.	2-75W Med. Base **or** 18W CFL	-
QM6904M	29" H, 19" W, 19" Dp.	1-150W Med. Base **or** 40W CFL	5" x 19" x 12"

Table & Floor

Please see referenced page numbers for larger images and full descriptions of these products.

Kyle
KY6328IB
See page 73

Union Station
UST6127WT
See page 140

CAROLYN KiNDER
Confetti
CKCF6330OS
See page 208

CAROLYN KiNDER
Brookmont
CKBT1863T
See page 212

CAROLYN KiNDER
Hickman
CKHM1879T
See page 212

Laguna
MC842TRC
See page 229

Laguna
MC842FRC
See page 229

Laguna
Q4574A
See page 232

Alistar
MCAL9470IB
See page 233

Alistar
MC1862IB
See page 233

Prism
MC2042T
See page 233

Cyrus
MCCS9357AS
See page 234

Cyrus
MCCS9470AS
See page 234

Cyrus
MCCS6326AS
See page 234

San Gabriel
NX615TVA
See page 234

Pearce
PER6323TB
See page 236

Table & Floor

Please see referenced page numbers for larger images and full descriptions of these products.

Vega

MC1691TIB

See page 236

Highland

MC120T

See page 237

Tartan

MC2134TWT

See page 238

Whispering Wood

AG711TVA

See page 238

Pomez

TF135TBC

See page 243

Pomez

TF6825CN

See page 243

Pomez

TF135FBC

See page 243

Captiva

SSCV6222VB

See page 244

Captiva

SSCV6224VB

See page 244

Floret

SSFT6221VB

See page 244

Sanibel

SSSB6223VB

See page 245

Jade

JD2077TVB

See page 245

*Please see the **Quoizel Tiffany Collection** on **page 459** for many attractive art glass table and floor lamp solutions.*

BRECKENRIDGE MIRROR
QR1419BN (p. 533)

Please see our Portables Catalog (CQP3017X) for an exclusive presentation of portable products and mirrors.

MIRRORS

QUOIZEL

Woodmere

NEW!
FOR ◆ 2016

QR1416

QR2060

Carrigan

GLASS: Beveled Frame and Mirror

Hearst

FINISH: **2053** Gold Leaf
2054 silver Leaf

QR2053

QR2057

NEW!
FOR ◆ 2016

NEW!
FOR ◆ 2016

QR2054

QR2058

Vanderbilt

FINISH: **2058** Palladian Bronze
2057 Century silver Leaf

PRODUCT	DIMENSIONS
QR1416	32" H, 26" W, 2" Dp.
QR2053/2054	30.5" H, 20.5" W, 3" Dp.

PRODUCT	DIMENSIONS
QR2060	39.5" H, 24" W, 1" Dp.
QR2057/2058	36" H, 24" W, 1" Dp.

NEW!
FOR ◆ 2016

Finn

FINISH: Palladian Bronze

QR2059

QR1253

Sage

Tallon

FINISH: **2055** ivory with Gold Highlights
2056 Century silver Leaf

NEW!
FOR ◆ 2016



QR2056



QR2055

QR42420BN

Soho

FINISH: Brushed Nickel

PRODUCT	DIMENSIONS
QR1253	30" H, 24" W, 1" Dp.
QR2055/2056	36" H, 36" W, 2" Dp.

PRODUCT	DIMENSIONS
QR2059	42" H, 42" W, 1" Dp.
QR42420BN	24" H, 20" W, 1.5" Dp.

Duchess

FINISH: Palladian Bronze
GLASS: Beveled

See p. 347 for matching Duchess products.

DH44030PN

DH43024PN

Greystone

GLASS: Frameless, Beveled

QR1815

See setting shot for QR1815 on page 341.

Jasper

FINISH: Brushed Nickel
GLASS: Beveled

JA43225BN

TY43625AN

Taylor

FINISH: Antique Nickel
GLASS: Beveled

See p. 367 for matching Taylor products.
See setting shot for TY43625AN on page 366.

PRODUCT	DIMENSIONS
DH43024PN	30" H, 24" W, 1.5" Dp.
DH44030PN	40" H, 30" W, 1.5" Dp.
JA43225BN	32" H, 24.5" W, 2" Dp.

PRODUCT	DIMENSIONS
QR1815	28" H, 22" W, 1" Dp.
TY43625AN	35.5" H, 25.5" W, 2" Dp.

QR983



Gwyneth

GLASS: Beveled

MY430241ML

QUOIZEL
NATURALS
PEN SHELL

MY430242ML

QR1922WT

Monterey Mosaic

FINISH: Malaga

See pages 81-86 for matching Monterey Mosaic products.
See setting shot for MY430241ML on pages 82-83.

Maxim

FINISH: Western Bronze

QR1864C

Shelburne

FINISH: Polished Chrome

PRODUCT	DIMENSIONS
MY430241ML	30" H, 24" W, 1.5" Dp.
MY430242ML	30" H, 24" W, 1.5" Dp.
QR983	39.5" H, 39.5" W, 2" Dp.

PRODUCT	DIMENSIONS
QR1922WT	37.5" H, 25" W, 1" Dp.
QR1864C	33" H, 25.5" W, 1" Dp.

Downtown

FINISH: Brushed Nickel

See p. 46-51 for matching Downtown products.

DW43222BN

QR1221C

Norton

FINISH: Polished Chrome

Ritz

FINISH: Polished Chrome
GLASS: Beveled

Envision

GLASS: Frameless, Beveled

UPRZ43426C

UPTOWN by SERGIO OROZCO NEW YORK

UPRZ53426C

QR1814

PRODUCT	DIMENSIONS
DW43222BN	32" H, 22" W, 1.5" Dp.
QR1221C	32" H, 22" W, 1.5" Dp.
QR1814	28" H, 22" W, 1" Dp.

PRODUCT	DIMENSIONS
UPRZ43426C	34" H, 26" W, 2" Dp.
UPRZ53426C	34" H, 26" W, 2" Dp.

QR1419PN

QR1419BN

Breckenridge

FINISH: **BN** Brushed Nickel
PN Palladian Bronze
GLASS: Beveled

Marcos

FINISH: Brushed Nickel

QR1857BN

QR1912WT

Vista

FINISH: Western Bronze

Ultra

GLASS: Beveled Frame and Mirror

NEW!
FOR ◆ 2016

CKCF43624OS

Confetti

FINISH: old silver

See pages 208-209 for matching Confetti products.

Carolyn Kinder INTERNATIONAL

CKUT1921

PRODUCT	DIMENSIONS
CKCF43624OS	35" H, 24" W, 1" Dp.
CKUT1921	36" H, 24" W, 2" Dp.
QR1419BN/PN	35" H, 21" W, 1" Dp.

PRODUCT	DIMENSIONS
QR1857BN	32" H, 24" W, 1" Dp.
QR1912WT	30" H, 30" W, 1" Dp.

MINI PENDANT RODS

Darkest Bronze

Imperial Bronze

Iron Gate

Mystic Black (matte)

Mottled Black

Mottled Silver

Vintage Gold

9006EX 6" H, .5" W, .5" Dp.	**9012EX** 12" H, .5" W, .5" Dp.	
9006EXAN	**9012EXAN**	Antique Nickel
9006EXBA	**9012EXBA**	Royal Ebony
9006EXBN	**9012EXBN**	Brushed Nickel
9006EXC	**9012EXC**	Polished Chrome
9006EXCC	**9012EXCC**	Copper Canyon
9006D	**9012EXD**	Dusk Bronze
9006EXDC	**9012EXDC**	Dark Cherry
9006EXDK	**9012EXDK**	Darkest Bronze
9006EXES	**9012EXES**	Empire Silver
9006EXIB	**9012EXIB**	Imperial Bronze
9006EXIF	**9012EXIF**	Italian Fresco
9006EXIN01	**9012EXIN01**	Iron Gate
9006EXIS	**9012EXIS**	Imperial Silver
9006EXK	**9012EXK**	Mystic Black (matte)
9006EXK01	**9012EXK01**	Mystic Black (glossy)
9006EXLN	**9012EXLN**	Leathered Bronze
9006EXMB	**9012EXMB**	Mottled Black
9006EXMC	**9012EXMC**	Mottled Cocoa
9006EXML	**9012EXML**	Malaga
9006EXMM	**9012EXMM**	Mottled Silver
9006EXMN	**9012EXMN**	Millenia
9006EXOS	**9012EXOS**	Old Silver
9006EXOZ1	**9012EXOZ1**	Old Bronze
9006EXPN	**9012EXPN**	Palladian Bronze
9006EXRC	**9012EXRC**	Renaissance Copper
9006EXRK	**9012EXRK**	Rustic Black
9006EXRS	**9012EXRS**	Russet
	9012EXTB	Terra Bronze
9006EXTM	**9012EXTM**	Teco Marrone
9006EXVA	**9012EXVA**	Valiant Bronze
9006EXVB	**9012EXVB**	Vintage Bronze
9006EXVG	**9012EXVG**	Vintage Gold
9006EXWT	**9012EXWT**	Western Bronze

9016EXPN (16" L)	Palladian Bronze

9007EX, 9106EX
6" H, 1" W, 1" Dp.

9008EX, 9112EX
12" H, 1" W, 1" Dp.

9007EXAN	**9008EXAN**	Antique Nickel
9007EXBN01	**9008EXBN01**	Brushed Nickel
9007EXC	**9008EXC**	Polished Chrome
9007EXCC	**9008EXCC**	Copper Canyon
9007EXIS	**9008EXIS**	Imperial Silver
9007EXMM	**9008EXMM**	Mottled Silver
9007EXOS	**9008EXOS**	Old Silver
9007EXPN	**9008EXPN**	Palladian Bronze
9007EXRK	**9008EXRK**	Rustic Black
9007EXVA	**9008EXVA**	Valiant Bronze
9007EXWT	**9008EXWT**	Western Bronze
9106EXBN	**9112EXBN**	Brushed Nickel

Antique Nickel

Brushed Nickel

Imperial Silver

Palladian Bronze

Western Bronze

Finish Sample Guide

Quoizel lamps, lighting fixtures and mirrors are created in a variety of decorative finishes. Finish samples are available upon request. Please contact your sales representative for details.

OUTDOOR LIGHTING

Pier Mounts

PM9300IB

PM9300Z

Enlarged for detail

PM9300K

For Ground Mounting:
Please order post (PO9110 followed by a finish code).

For Column Mounting:
Please order pier mount (PM9300 followed by a finish code).

Please note:
The post does not fit into the pier mount.

Post Mounts

PO9110IB

PO9110Z

PRODUCT	DIMENSIONS	FINISH
PM9300IB/K/Z	3.5" H, 6" W, 6" Dp.	IB = Imperial Bronze K = Mystic Black Z = Medici Bronze
PO9110IB/Z	84" H, 3" W, 3" Dp.	IB = Imperial Bronze Z = Medici Bronze

PO9120IB

PO9120K

PO9120Z

Round post detail

PO9140K

PO9140Z

Post Mounts

P09120 – Round Post
P09130 – Fluted Post

Fluted post detail

PO9130IB

PO9130K

PO9130Z

Post & skirt

PO9140IB

Enlarged for detail

PRODUCT	DIMENSIONS	FINISH
PO9120IB/K/Z	84" H, 3" W, 3" Dp.	IB = Imperial Bronze K = Mystic Black Z = Medici Bronze
PO9130IB/K/Z	84" H, 3" W, 3" Dp.	IB = Imperial Bronze K = Mystic Black Z = Medici Bronze
PO9140IB/K/Z	81" H, 10" W, 10" Dp.	IB = Imperial Bronze K = Mystic Black Z = Medici Bronze

A

AB701A 523
AB702A 523
AB703A 523
ABN5006RK 143, 144, 251
ABN5012RK 144, 251
ABN5024RK 142, 251
ADA2820LN 103, 273
ADA5006LN 103
ADA5009LN 102
ADA8702LN 103, 319
ADS1504DC 39, 284
ADS1615DC 39, 308
ADS2818DC 39, 272
ADS5005DC 38
ADS639DC 39, 255
ADS8701DC 38, 319
AG711TVA 238, 526
AI1720IB 240, 301
AI2824IB 240, 277
ALT8405WT 380
ALT8407WT 380
AME5005IB 109, 249
AME5009IB 109, 249
AME5018IB 108, 249
AME8701IB 109, 249, 319
AML2821OZ 265
AML5005OZ 162
AN8539ES 342
AN8540ES 342
AN8541ES 342
ANR5006IB 171, 252
ANR5010IB 171, 252
AS1716PN 241, 301
AS2818PN 241, 277
AS2824PN 241, 277
AX2820PN 104, 273
AX2826PN 104, 273
AX434PN 104, 254

B

BAN1911K 450
BAN8407K 450
BAN8409K 450
BAN8411K 448, 449
BAN9011K 450
BCN1716WT 45, 298
BCN2820WT 45, 272
BCN5006WT 45
BCN5009WT 44
BCN5204WT 45
BDR2820IB 238, 277
BDR5006IB 160, 251
BFD1910K 395
BFD1910PN 395
BFD8407K 395
BFD8407PN 395
BFD8408K 395
BFD8408PN 395
BFD8410K 394
BFD8410PN 395
BFD9010K 395
BFD9010PN 395
BGS1715RK 288
BGS5203RK 170
BGT8602BN 343
BGT8603BN 343
BGT8604BN 343
BHN5006VG 157, 251
BHN5009VG 157, 251
BHN5303VG 157, 251
BKH1714WT 42, 298
BKH5204WT 43
BKH5208WT 43
BKH5303WT 43
BKH838WT 42, 254
BKR1910K 405
BKR8406K 405
BKR8408K 371, 405
BKR8410K 404
BKR9010K 405
BND1613BA 307
BND1818BA 268
BNS1505WT 40, 284
BNS1715WT 41, 298
BNS2818WT 41, 272
BNS5005WT 41
BNS5009WT 40
BNS5204WT 41
BRN1910IB 435
BRN8406IB 435
BRN8408IB 435
BRN8410IB 435
BRN8412IB 434
BRN9010IB 435
BRO1715MK 110, 250, 299
BRO5203MK 110, 250
BRO5204MK 110, 249
BRX1611C 176, 308
BRX1614C 175, 308
BRX1619C 175, 308
BRX1620C 176, 309
BRX1626C 176, 309
BRX2818C 174, 274
BRXA1614C 175, 308
BRXA1619C 175, 308
BWL1508CC 280
BWL1717CC 288
BWL2816CC 267
BWL2822CC 267
BWR8602BN 346
BWR8603BN 346
BWR8604BN 346

C

CAT1911PN 389
CAT8407PN 389
CAT8409PN 389
CAT8411PN 388
CAT9011PN 389
CATL1911PN 387
CATL8407PN 387
CATL8409PN 387
CATL8411PN 386
CATL9011PN 387
CCR8406CU 441
CCR8408CU 441
CCR8410CU 441
CCR9010CU 441
CDY1508BN 280
CDY1714BN 297
CDY2814BN 270
CHB1612DK 106, 249, 308
CHB5204DK 106, 107, 249
CHB5206DK 106, 249
CHB5208DK 106, 249
CHI1911IB 457
CHI8407IB 457
CHI8409IB 457
CHI8411IB 457
CHI8413IB 456
CHI9011IB 457
CKBT1863T 212, 525
CKCF1508OS 209, 285
CKCF1508RK 209, 285
CKCF1714OS 209, 300
CKCF1717OS 209, 300
CKCF1717RK 209, 300
CKCF1720OS 209, 300
CKCF2816OS 209, 275
CKCF2816RK 209, 275
CKCF2822OS 207, 209, 275
CKCF2822RK 208, 275
CKCF2825OS 208, 275
CKCF2825RK 209, 275
CKCF3390S 209, 258
CKCF339RK 208, 258
CKCF43624OS 208, 533
CKCF6330OS 208, 525
CKGN1509MZ 215, 286
CKHM1879T 212, 525
CKKD1509WT 214, 215, 286
CKMO1716BN 210, 300
CKMO2820BN 210, 275
CKMO5003BN 210, 211
CKMS1716TM 213, 300
CKMS2822TM 213, 276
CKMS442TM 213, 257, 258
CKNK1509BV 215, 286
CKSC5201DR 212
CKSN1507AR 215, 286
CKUT1921 ..... 212, 533
CLT1714BN 289
CLT5004BN 162
CM1912AC 422
CM8408AC 422
CM8410AC 423
CM8412AC 422
CM9012AC 422
COE8305WT 381
COE8405WT 381
COR1611CU 425
COR1611K 425
COR8409K 425
COR8410K 425
COR8412K 424
COR9010K 425
CP2820IB 268
CP5006IB 160
CRA1717MC 290
CRA2822MC 271
CRA2826MC 271
CRE5004FR 151
CS1718RK 111, 250, 299
CS5006RK 111, 250
CS5012RK 111, 250
CTH5003AN 147
CTH5006AN 147
CTH5009AN 146
CTH5204AN 147
CTO5204WT 168
CVW8406WT 401
CVW8407WT 401
CVW8408WT 401

D

DBN1506BN 282
DBN8602BN 345
DBN8603BN 344, 345
DBN8604BN 345
DE1490IB 429
DE8958IB 429
DE8959IB 429
DE8960IB 429
DE8961IB 428
DE8976IB 429
DE9256IB 429
DH1404AN 56, 312
DH1404PN 57, 311, 312
DH1506AN 57, 284
DH1506PN 56, 284
DH1718AN 57, 298
DH1718PN 56, 298
DH2820AN 54, 272
DH2820PN 54, 55, 272
DH348AN 54, 259
DH348PN 54, 259
DH43024PN 57, 530
DH44030PN 57, 530
DH5005AN 53
DH5005PN 53
DH5009AN 52
DH5009PN 53

DH5018AN....53
DH5018PN....53
DH5103AN....54
DH5103PN....54
DH5105AN....53
DH5105PN....53
DH8601AN....57, 319, 347
DH8601PN....57, 319, 347
DH8602AN....57, 347
DH8602PN....57, 347
DH8603AN....57, 347
DH8603PN....57, 347
DH8604AN....57, 347
DH8604PN....57, 347
DI8502C....352
DI8502ES....354
DI8503C....352
DI8503ES....353, 354
DI8504C....352
DI8504ES....354
DUN5203GK....155
DUN5204GK....155
DVN8602BNLED....333
DVN8602CLED....333
DVN8603BNLED....333
DVN8603CLED....333
DVN8604BNLED....333
DVN8604CLED....333
DW1506C....51, 284
DW1506D....51, 284
DW1717C....51, 298
DW1717D....51, 298
DW1824C....51, 272
DW1824D....51
DW2817C....50, 51, 272
DW2817D....51
DW43222BN....49, 532
DW5004C....48
DW5004D....48
DW5005C....47, 48
DW5005D....48
DW5009C....48
DW5009D....48
DW5015C....46
DW5015D....46
DW8602BNLED....49, 335
DW8602CLED....49, 334
DW8603BNLED....49, 335
DW8603CLED....49, 334
DW8604BNLED....49, 335
DW8604CLED....49, 334
DW8701BN....49, 319, 335
DW8701C....49, 319, 321, 334
DX1718C....290, 291
DX348C....253, 261
DX8601C....349
DX8602C....349
DX8603C....349
DX8604C....349

E

EDS8601WT....350
EDS8602WT....350
EDS8603WT....350
EDS8604WT....350
EME8604C....197, 369
EME8606C....197, 369
EME8608C....197, 369
ER1508BN....62, 284
ER1508IS....62, 284
ER1508PN....62, 284
ER1814BN....62, 272
ER1814IS....62, 63, 272
ER1814PN....62, 272
ER353BN....62, 255
ER353IS....62, 255
ER353PN....62, 255
ER5103BN....61
ER5103IS....61
ER5103PN....61
ERN8602IBLED....336
ERN8603IBLED....336
ERN8604IBLED....336
EST5204IB....154
EST5206IB....154
EST5208IB....154
EVE1404PN....105, 313
EVE1508PN....105, 285
EVE240PN....105, 256
EVE2815PN....105, 273

F

FE1506WT....280
FQ1920MK01....392
FQ1931MK01....392
FQ8407AW....391
FQ8407MK....391, 393
FQ8409AW....391
FQ8409MK....391
FQ8411AW....391
FQ8411MK....391
FQ8414AW....390
FQ8414MK....391
FQ9011AW....391
FQ9011MK....391
FTR1713IB....288
FTR5204IB....161

G

GCT5204WT....168
GF1617AN....305
GF1617PN....305
GF1621AN....305
GF1621PN....305
GF1717AN....294
GF1717PN....294, 295
GF1721AN....294
GF1721PN....294
GLN1910IB....440
GLN8407IB....440
GLN8409IB....439, 440
GLN8410IB....440
GLN8412IB....438
GLN9010IB....440
GRN8602BN....351
GRN8602WT....351
GRN8603BN....351
GRN8603WT....351
GRN8604BN....351
GRN8604WT....351
GRT1508BN....101, 115, 285
GRT1508IS....115, 285
GRT1508PN....115, 285
GRT2814BN....115, 273
GRT2814IS....115, 273
GRT2814PN....115, 273
GRT5103BN....114
GRT5103IS....114
GRT5103PN....114
GT1700IB....455
GT8980IB....455
GT8981IB....455
GT8982IB....454
GT9294IB....455
GVR1910K....453
GVR8406K....453
GVR8408K....453
GVR8410K....452
GVR9010K....453

H

HC1109IBFL....412
HC1612IB....415
HC1909IB....415
HC1909IBFL....412
HC1913IB....415
HC1913IBFL....412
HC8406IB....413
HC8406IBFL....412
HC8407IB....413
HC8407IBFL....412
HC8409IB....413
HC8409IBFL....412
HC8411IB....413
HC8411IBFL....412
HC8413IB....412, 414
HC8413IBFL....412
HC8506IBFL....412
HC8507IBFL....412
HC8509IBFL....412
HC8511IBFL....412
HC8513IBFL....412
HC9011IB....415
HC9011IBFL....412
HC9013IB....415
HC9013IBFL....412
HC9111IBFL....412
HCE8409IB....413
HCE8409IBFL....412
HCE8411IB....413
HCE8411IBFL....412
HCE8509IBFL....412
HCE8511IBFL....412
HK5005TC....166, 252
HK5008TC....166, 252
HS8601C....348
HS8602C....348
HS8603C....348
HS8604C....348
HTR1908IB....407
HTR8406IB....407
HTR8407IB....407
HTR8408IB....406
HTR9008IB....407
HY1911IB....411
HY8407IB....411
HY8407IBFL....410
HY8409IB....411
HY8409IBFL....410
HY8411IB....411
HY8413IB....410
HY8507IBFL....410
HY8509IBFL....410
HY8513IBFL....410
HY9011IB....411

J

JA43225BN....530
JD2077TVB....245, 526
JLE1709IS....296
JLE2809IS....269
JLE2812IS....269
JV2816OS....265
JV2820OS....265

K

KD1507MM....67, 246, 284
KD1716MM....67, 246, 298
KD2816MM....67, 246, 272
KD2824MM....67, 246, 272
KD5005MM....65, 246
KD5009MM....65, 66, 246
KD5015MM....64, 246
KD8701MM....65, 246, 319

KDN1510BN 252, 280
KDN5004BN 169, 252
KLT8602CLED 340
KLT8603CLED 340, 341
KLT8604CLED 340
KPR5005BN 162
KY1404IB 72, 247, 312, 314
KY1507IB 69, 73, 247, 284
KY1507IN 73, 247, 284
KY1508IB 73, 247, 284
KY1508IN 73, 247, 284
KY1716IB 72, 247, 298
KY2822IB 69, 72, 247, 272
KY433IB 71, 247, 260
KY5006IB 71, 247
KY5006IN 70, 247
KY5009IB 71, 247
KY5009IN 70, 247
KY5016IB 68, 247
KY5103IB 71, 247
KY5103IN 71, 247
KY5106IB 70, 247
KY540IB 71, 247, 260
KY540IN 71, 247, 260
KY5503IB 72, 247
KY5506IB 72, 247
KY6328IB 73, 227, 247, 525
KY8701IB 73, 247, 319
KY8701IN 73, 247, 319
KY8801IB 73, 247, 319
KY8801IN 73, 247, 319

L

LBH2820WT 271
LDG1909K 417
LDG8406K 417
LDG8408K 417
LDG8409K 416
LDG9009K 417
LFT8602C 355
LFT8603C 355
LFT8604C 355
LKE5204VG 141, 168
LLA1615RA 116, 308
LLA5203RA 116
LLA5204RA 116
LLA5205RA 116
LP1505IB 76, 284
LP5006IB 75
LP5009IB 75
LP5018IB 74
LP639IB 76, 259
LP8601IB 76, 319
LSM8801GY 318
LSM8801PS 318
LSM8801TM 318

M

MBH1911K 400
MBH1911PN 400
MBH8407K 400
MBH8407PN 399, 400
MBH8409K 400
MBH8409PN 400
MBH8411K 398
MBH8411PN 398
MBH9011K 400
MBH9011PN 400
MBK1716VG 113, 299
MBK2820VG 113, 273
MBK5005VG 112, 113
MC120T 237, 526
MC1691TIB 236, 526
MC1862TIB 233, 525
MC1910MM 235, 277
MC2042T 233, 525
MC2134TWT 238, 526
MC8420CRC 228, 276, 277
MC842CRC 228, 231, 277
MC842FRC 229, 525
MC842PRC 230, 232, 286
MC842SRC 228, 301
MC842TRC 229, 525
MCAL9470IB 233, 525
MCBF1717WT 237, 301
MCBF2822WT 237, 277
MCCS6326AS 234, 525
MCCS9357AS 234, 525
MCCS9470AS 234, 525
MCKD1505TM 235, 286, 301
MCKD1715TM 235, 301
MCKD2819TM 235, 277
MCLG1612RC 229, 310
MCLG1616RC 229, 310
MCLG337RC 232, 254
MHE1910K 419
MHE1910VN 419
MHE8406K 419
MHE8406VN 419
MHE8409K 419
MHE8409VN 419
MHE8410K 419
MHE8410VN 418
MHE9010K 419
MHE9010VN 419
MIR1715VG 296
MIR1718VG 296
MIR2818VG 269
MJT5004BN 165
MJT5006BN 165
MJT5008BN 164
MJY1615VG 296
MJY5304VG 159
ML182AUL 302
ML182ESUL 302
ML182PNUL 302
ML182WUL 302
ML183A 302
ML183ES 302
ML183PN 302
ML183W 302
ML184A 302
ML184ES 302
ML184PN 302
ML184W 302
MLD8602BN 356
MLD8603BN 356
MLD8604BN 356
MLN8307K 458
MLN8309K 458
MLS1907IB 403
MLS8405IB 403
MLS8406IB 403
MLS8407IB 402
MLS9007IB 403
MMR5303C 159
MNO5006WT 167
MNO8602IS 357
MNO8603IS 357
MNO8604IS 357
MNR1611BN 303
MNR1611PN 303
MNR1613BN 303
MNR1613PN 303
MNR1615BN 303
MNR1615PN 303
MNT8404WT 372
MNT8405WT 372
MQ5003HL 77, 80
MQ5006HL 79
MQ5009HL 79
MQ5020HL 78
MQ5206HL 80
MQ5208HL 80
MQ8701HL 79, 319
MRE1506WT 281, 427
MRE1909WT 427
MRE8406WT 427
MRE8408WT 427
MRE8409WT 427
MRE8410WT 426
MRE9009WT 427
MRN5005IB 145
MRN5006IB 145
MRN5008IB 145
MTP1510AN 117, 285
MTP1718AN 117, 299
MTP2820AN 117, 273
MTP2823AN 117, 273
MTP5203AN 117
MY1404ML 85, 248, 312
MY1506ML 86, 248, 284
MY1613ML 85, 248, 308
MY1618ML 85, 248, 308
MY1718ML 85, 248, 298
MY1723ML 85, 248, 298
MY2816ML 84, 248, 273
MY2824ML 84, 248, 273
MY430241ML 82, 86, 248, 531
MY430242ML 86, 248, 531
MY5005ML 81, 248
MY5103ML 83, 84, 248
MY8801ML 83, 86, 248, 319

N

NA1510BN 119, 285
NA1514BN 119, 285
NA5103BN 118
NA8409PN 119, 458
NA8414PN 119, 458
NBE5005RK 129
NBE5008RK 129
NBE5009RK 128
NBE5303RK 129
NBE8702RK 129, 320
NGT8602BN 361
NGT8603BN 361
NGT8604BN 361
NHR1718WT 133, 299
NHR5204WT 133
NHR538WT 133, 256
NL8601BN 360
NL8601C 360
NL8601HO 360
NL8602BN 360
NL8602C 360
NL8602HO 360
NL8603BN 360
NL8603C 360
NL8603HO 360
NL8604BN 360
NL8604C 360
NL8604HO 360
NN8602BNLED 339
NN8603BNLED 339
NN8604BNLED 339
NX615TVA 234, 525
NY1178A 378
NY1178AC 377
NY1178B 377
NY1178K 377
NY1178P 377
NY1178Z 377
NY1179A 377
NY1179AC 379
NY1179B 377
NY1179K 377
NY1179P 377
NY1179Z 377
NY1180A 377
NY1180AC 379
NY1180B 377

NY1180K 377
NY1180P 377
NY1180Z....377
NY1615K 374
NY1615P 375
NY1615Z....375
NY1794B 377
NY1794K 377
NY1794P 377
NY1794Z....377
NY1909K 375
NY1909P 375
NY1909Z....375
NY1912K 375
NY1912P 375
NY1912Z....375
NY1916K 375
NY1916P 375
NY1916Z....375
NY8315A 377
NY8315AC....377
NY8315B 377
NY8315K 377
NY8315P 377
NY8315Z....377
NY8316A 377
NY8316AC....377
NY8316B 377
NY8316K 377
NY8316P 379
NY8316Z....377
NY8317A 377
NY8317AC....377
NY8317B 377
NY8317K 377
NY8317P 379
NY8317Z....377
NY8318A 377
NY8318AC....377
NY8318B 377
NY8318K 378
NY8318P 377
NY8318Z....377
NY8339A 377
NY8339AC....377
NY8339B 377
NY8339K 377
NY8339P 376
NY8339Z....377
NY8407K 375
NY8407P 374
NY8407Z....375
NY8409K 374
NY8409P 375
NY8409Z....375
NY8411K 375
NY8411P 374
NY8411Z....375
NY8412K 375
NY8412P 375
NY8412Z....374
NY8416K 375
NY8416P 375
NY8416Z....374
NY9011K 375
NY9011P 375
NY9011Z....375
NY9012K 375
NY9012P 375
NY9012Z....375
NY9016K 375
NY9016P 375
NY9016Z....375
NY9042A 377
NY9042AC....377
NY9042B 377
NY9042K 377
NY9042P 377
NY9042Z....377
NY9043A 378
NY9043AC....377
NY9043B 377
NY9043K 377
NY9043P 377
NY9043Z....377
NY9045A 377
NY9045AC....377
NY9045B 377
NY9045K 378
NY9045P 377
NY9045Z....377
NYL1911K....373
NYL8407K....373
NYL8409K....373
NYL8411K....373
NYL9011K....373

O

OAS1909Z....409
OAS8406Z....409
OAS8408Z....409
OAS8409Z....409
OAS8411Z....409
OAS8413Z....408
OAS9009Z....409
OAS9011Z....409
ODL2820IB....125, 251, 274
ODL5005IB....125, 251
ODL5009IB....124, 250
ODL5206IB....125, 251
ODL5303IB....125, 251
ON2818BN....264
ON2818WT....264
ON2824BN....264
ON2824WT....264
OPA1613WT....127, 308
OPA1617WT....127, 308
OPA5005WT....126
OPA5304WT....127
OZ1613IN....306
OZ1613PN....306
OZ1616IN....287, 306
OZ1616PN....306
OZ1713IN....293
OZ1713PN....293
OZ1716IN....293
OZ1716PN....293

P

PB5004TK....170, 252
PB5008TK....170, 252
PCAE1715C....190, 300
PCAE2820C....190, 275
PCAN2814C....180, 274
PCAX1714C....179, 300
PCAX8603CLED....195, 327
PCAX8604CLED....195, 327
PCAY1722C....190, 300
PCBD8519C....204, 324
PCBD8526C....204, 324
PCBM8505C....206, 322
PCBM8520C....206, 322
PCBM8526C....206, 322
PCCF2824C....177, 180, 274
PCCR1717C....180, 300
PCCT1616C....179, 309
PCCT1623C....179, 309
PCDH8522BN....203, 326
PCDH8530BN....203, 326
PCDV8602CLED....202, 332
PCDV8603CLED....202, 332
PCDV8604CLED....202, 332
PCEC1820MN....192, 275
PCED8517C....195, 323
PCED8521C....195, 323
PCED8528C....195, 323
PCEL1616C....184, 309
PCEL1623C....184, 309
PCGL8522BN....203, 326
PCGL8530BN....203, 326
PCGX1817C....178, 274
PCGX1826C....178, 274
PCHE1616C....183, 309
PCHE1620C....183, 309
PCJL2820C....183, 274
PCLC8603CLED....201, 331
PCLC8605CLED....201, 331
PCMR8603CLED....201, 331
PCMR8605CLED....201, 331
PCMY2818C....181, 191, 274
PCPC8527C....205, 325
PCPC8533C....205, 325
PCPE8524C....205, 325
PCPE8536C....205, 325
PCPR8522BN....198, 323
PCPR8530BN....198, 323
PCSA8602BNLED....200, 330
PCSA8603BNLED....200, 330
PCSA8604BNLED....200, 330
PCSL1616C....192
PCSP1718C....184, 300
PCSP2823C....184, 274
PCSR1716C....181, 300
PCSR8602CLED....194, 328
PCSR8603CLED....194, 328
PCSR8604CLED....194, 328
PCSW8601BNLED....199, 329
PCSW8601CLED....199, 329
PCSW8602BNLED....199, 329
PCSW8602CLED....199, 329
PCSW8603BNLED....199, 329
PCSW8603CLED....199, 329
PCSW8604BNLED....199, 329
PCSW8604CLED....199, 329
PCTS1503C....181, 285
PCVN1716C....182, 300
PCVN2820C....182, 196, 274
PCVT8518BN....204, 324
PCVT8524BN....204, 324
PER1715TB....236, 301
PER6323TB....236, 525
PF1405C....313
PF8602ES....359
PF8603ES....358, 359
PF8604ES....359
PLR1716PN....122, 299
PLR2820PN....122, 273
PLR5005PN....122
PM9300IB....536
PM9300K....536
PM9300Z....536
PO9110IB....536
PO9110Z....536
PO9120IB....537
PO9120K....537
PO9120Z....537
PO9130IB....537
PO9130K....537
PO9130Z....537
PO9140IB....537
PO9140K....537
PO9140Z....537
PRL8601PK....362
PRL8602PK....362
PRL8603PK....362
PRN1614C....182, 309

PRN8604C 193, 368
PRN8606C 193, 368
PRN8608C 193, 368
PRV1909K 445
PRV8406K 445
PRV8408K 445
PRV8409K 444
PRV9009K 445
PTD2820BN 267
PTD2820WT 267
PTD2826BN 267
PTD2826WT 266
PWL1613WT 447
PWL8307WT 447
PWL8309WT 447
PWL8311WT 446
PWL9009WT 447

Q

Q1054FBN 514
Q1054FPN 514
Q1054TBN 514
Q1054TPN 514
Q1055FBN 515
Q1055FPN 515
Q1056FBN 514
Q1056FPN 507, 514
Q1072FPN 515
Q1072TPN 515
Q1073FPN 515
Q1074FPN 515
Q1295KPK 524
Q1630FPN 522
Q1632TPN 513
Q1633FBN 513
Q1634FPN 513
Q1634TBN 513
Q1634TPN 513
Q1852TAB 516
Q1852TBN 516
Q1889FOI 517
Q1892FOI 517
Q1893FOI 517
Q1914T 517
Q1915T 517
Q1918TBN 516
Q1918TPN 516
Q1919TAB 516
Q1919TPN 516
Q2125TBN 518
Q2125TWT 518
Q2126FWT 519
Q2126TWT 519
Q2127TWT 520
Q2310F 519
Q2310F1 519
Q2311T 519
Q2311T1 519
Q2312T 518
Q2312T1 518
Q2313T 518
Q2313T1 518
Q2314T 520
Q2315T 520
Q2316T 520
Q2316T1 520
Q2317T 521
Q2318T 521
Q2319T 521
Q2320T 521
Q2321T 521
Q2322T 522
Q2323T 522
Q2324T 522
Q2325T 523
Q4571A 524
Q4574A 232, 525
QF1201SWT 293
QF1202SWT 293
QF1213SBN 289
QF1213SHO 289
QF1402CMU 161
QF1678BN 297
QF1715WT 292
QF1820MB 161
QF1829VG 171
QF1829WT 171
QF1831BN 297
QF1834BN 297
QF1834WT 297
QF1839RK 155
QF1840RK 166, 252
QF2046C 263, 270
QF2047C 279
QI8602CLED 338
QI8603CLED 338
QI8604CLED 338
QJ6781TR 524
QJF15078BTR 524
QM6904M 524
QMC1199FR 150, 151
QMC404BO 158, 159
QPP1401WT 281
QPP2048BN 282
QPP2049BN 279
QPP2049WT 279
QPP2050BN 282
QPP2051IS 283
QR1221C 532
QR1253 529
QR1416 528
QR1419BN 527, 533
QR1419PN 533
QR1814 532
QR1815 ..... 341, 530
QR1857BN 533
QR1864C 531
QR1912WT 533
QR1922WT 531
QR2053 528
QR2054 528
QR2055 529
QR2056 529
QR2057 528
QR2058 528
QR2059 529
QR2060 528
QR42420BN 529
QR983 531
QTR10054PN 313

R

RBN1512C 189, 285
RBN1512CRC 187, 285
RBN1512MN 189, 285
RBN1512SG 189, 285
RBN1512W 189, 285
RBN1512WT 189, 285
RBN1616C 189, 310
RBN1616CRC 187, 309
RBN1616MN 189, 310
RBN1616SG 189, 310
RBN1616W 189, 310
RBN1616WT 189, 310
RBN1622C 189, 310
RBN1622CRC 187, 309
RBN1622MN 189, 310
RBN1622SG 189, 310
RBN1622W 189, 310
RBN1622WT 189, 310
RBN1628C 189, 310
RBN1628CRC 187, 310
RBN1628MN 189, 310
RBN1628SG 189, 310
RBN1628W 189, 310
RBN1628WT 189, 310
RBN2817C 189, 275
RBN2817CRC 186, 275
RBN2817MN 189, 275
RBN2817SG 189, 275
RBN2817W 189, 275
RBN2817WT 189, 275
RBN2823C 189, 275
RBN2823CRC 186, 275
RBN2823MN 189, 275
RBN2823SG 172, 189, 275
RBN2823W 189, 275
RBN2823WT 189, 275
RBN2831C 189, 275
RBN2831CRC 186, 275
RBN2831MN 189, 275
RBN2831SG 189, 275
RBN2831W 189, 275
RBN2831WT 188, 275
RDY1506CS 60, 284
RDY1714CS 59, 60, 298
RDY1714PN 60, 298
RDY2821CS 60, 272
RDY2821PN 60, 272
RDY2823CS 60, 272
RDY2823PN 60, 272
RDY5208CS 58
RDY5208PN 37, 58
REM345C 123, 261
REM5004C 123
REM8701C 123, 319
RGE1911WT 431
RGE8407WT 431
RGE8409WT 431
RGE8411WT 430
RGE9011WT 431
RJ1911K 433
RJ8407K 433
RJ8409K 433
RJ8411K 433
RJ8414K 432
RJ9011K 433
RLY1512IB 283
RLY1815IB 268
RO1914AC 421
RO8311AC 421
RO8410AC 421
RO8411AC 421
RO8414AC 420
RO9014AC 421
RYD8408WT 380
RYE8604C 198, 370
RYE8605C 198, 370

S

SDN1506IB 281, 437
SDN1908IB 437
SDN8405IB 437
SDN8407IB 437
SDN8408IB 437
SDN8409IB 436
SDN9008IB 437
SER5004IF 163
SER5006IF 163
SER5009IF 163
SFD1911IB 451
SFD8407IB 451
SFD8409IB 451
SFD8411IB 451
SL701G 523
SL702G 523
SL703G 523
SLR1716AN 292
SLR1716WT 292
SLR1720AN 292
SLR1720WT 292
SLT5004IF 156
SLT5006IF 156

SLT5303IF....156
SMT1612BN....304
SMT1612PN....304
SMT1614BN....304
SMT1614PN....304
SMT1617BN....304
SMT1617PN....304
SNN1612K....385
SNN1612PN....385
SNN1612W....385
SNN1909K....385
SNN1909PN....385
SNN1909W....385
SNN8406K....385
SNN8406PN....385
SNN8406W....385
SNN8408K....385
SNN8408PN....385
SNN8408W....385
SNN8409K....385
SNN8409PN....385
SNN8409W....384
SNN9009K....385
SNN9009PN....385
SNN9009W....385
SNNL1909K....383
SNNL1909PN....383
SNNL8406K....383
SNNL8406PN....383
SNNL8408K....383
SNNL8408PN....383
SNNL8409K....382
SNNL8409PN....383
SNNL9009K....383
SNNL9009PN....383
SPH1508BN....132, 285
SPH1508PN....132, 285
SPH5005BN....132
SPH5005PN....132
SPH5009BN....130
SPH5009PN....130, 131
SPR8601C....363
SPR8602C....363
SPR8603C....363
SPR8604C....363
SRA5204VG....169
SSCV6222VB....244, 526
SSCV6224VB....244, 526
SSFT6221VB....244, 526
SSSB1714VB....245, 301
SSSB6223VB....245, 526
SW2016X....535

T

TB8601C....365
TB8602C....365
TB8603C....365
TB8604C....365
TCA5004VP....137
TCA5006VP....137
TCA5009VP....136
TCA8701VP....137, 320
TDR1909K....397
TDR1909PN....397
TDR8406K....397
TDR8406PN....397
TDR8408K....397
TDR8408PN....397
TDR8409K....397
TDR8409PN....396
TDR9009K....397
TDR9009PN....397
TF1018TVB....480
TF1021TVB....502
TF1135F....492
TF1135T....492
TF1139T....494
TF1180TVA....472, 473
TF135FBC....243, 526
TF135TBC....243, 526
TF1396SVB....478
TF1400SVB....485
TF1408SVB....496
TF1409SVB....496
TF1425TWT....504
TF1427F....502
TF1427T....502
TF1433T....500
TF1438VB....459, 487
TF1487T....494
TF1507VB....242, 243, 286
TF1508TVB....491
TF1508FVB....491
TF1508VB....469
TF1536VB....278, 487
TF1541VB....484, 485
TF1575TIB....495
TF1618VB....487
TF1672TWT....492
TF1714VB....469
TF1737VB....487
TF1781VB....483
TF1783CIB....506
TF1784VB....499
TF1791TWT....486
TF1805SVB....469
TF1816VB....496
TF1846TIB....505
TF1848TIB....504
TF1850TIB....495
TF1851TIB....491
TF1860FZ....488
TF1860TZ....488
TF1868T....498
TF1873T....498
TF1901VB....499
TF1913TRS....505
TF1916TRS....503
TF1917TVA....505
TF2041T....506
TF2076FVB....500
TF2076TVB....500
TF2095TRS....503
TF489P01VB....501
TF489T....501
TF6031VB....493
TF6033VB....493
TF6034R....494
TF6599R....493
TF6660BB....485
TF6668VB....486
TF6669VB....497
TF6825CN....243, 526
TF6826VB....498
TF6898M....497
TF7110ZLED....488, 489
TF878CVB....477
TF878F....478
TF878T....478
TF878UVB....478
TF879F....475
TF879T....475
TF885F....480
TF885SVB....479
TF885T....481
TF9152ZLED....488
TF9320BB....485
TF9397VB....486
TF9404M....497
TFAS1404VA....315, 472
TFAS1507VA....471
TFAS1615VA....470
TFAS1714VA....472
TFAS1817VA....474
TFAS2817VA....471
TFAS344VA....262, 471
TFAS5003VA....470
TFAS9360VA....474
TFAS9470VA....474
TFAT1507VA....462
TFAT1716VA....462
TFAT2821VA....462
TFAT6325VA....463
TFAT9362VA....463
TFAV1714VB....501
TFBF348VB....262, 483
TFBF9362VB....483
TFCB6325VB....504
TFCC8802....320, 506
TFF16191A5VA....466
TFIK1404VA....315, 465
TFIK1508VA....465
TFIK1509VA....468
TFIK1617VA....468
TFIK1714VA....465
TFIK1817VA....464
TFIK2817VA....464, 467
TFIK348VA....262, 464
TFIK6111VA....468
TFIK8802....320, 468
TFIK9471VA....466
TFJD2822ML....490
TFJD2836ML....490
TFKM1508VB....477
TFKM2840VB....477
TFKM5103VB....476
TFMC1508WT....482
TFMC1715WT....482
TFMC1818WT....482
TFMC2818WT....482
TFMH1820VB....495
TFNO6325VA....503
TFST1508VB....480
TFST2822VB....479
TFST2840VB....479
TFST5103VB....479
TFST8701VB....320, 480
TFT16191A1VA....466
TFVY1404VA....315, 460
TFVY1716VA....460
TFVY2819VA....460
TFVY6118VA....461
TFVY6325VA....461
TFVY9359VA....461
TFX1518T....493
TFX1519T....493
TFX1520T....493
TFX837Y....493
THL1718MK....167
THL5006MK....167
TML1908K....443
TML8405K....443
TML8407K....443
TML8408K....442
TML9008K....443
TRG1508OZ....94, 284
TRG1712OZ....95, 299
TRG1716OZ....95, 299
TRG1816OZ....94, 273
TRG5103OZ....92, 94
TRG5105OZ....93
TRG8701OZ....95, 319
TT8604BN....364
TT8742BN....364
TT8743BN....364
TU8602BNLED....337
TU8603BNLED....337

TU8604BNLED....337
TVN1717DK....120, 250, 299
TVN232DK....120, 121, 250, 256
TVN5005DK....120, 250
TY1404AN....90, 316
TY1444AN....91, 316
TY1444WT....90, 316
TY1716AN....90, 298
TY1721AN....90, 298
TY43625AN....89, 91, 366, 530
TY5005AN....87, 88
TY628AN....90, 261
TY8501AN....87, 89, 319
TY8601AN....91, 319, 367
TY8601BN....91, 319, 367
TY8601C....91, 319, 367
TY8602AN....91, 367
TY8602BN....91, 367
TY8602C....91, 367
TY8602WT....91, 367
TY8603AN....91, 366, 367
TY8603BN....91, 367
TY8603C....91, 367
TY8603WT....91, 367
TY8604AN....91, 367
TY8604BN....91, 367
TY8604C....91, 367
TY8604WT....91, 367

U

UNS5204IB....169
UPCC5006IS....224
UPCN5006IS....221
UPCN5006WT....220, 221
UPCN5008IS....221
UPCN5008WT....221
UPEV5005WT....217
UPEV8701WT....216, 217, 320
UPFT1820IS....224, 276
UPHL8701IS....226, 320
UPMM5005WT....222, 223
UPMM8701WT....222, 223, 320
UPPS1510BN....225, 286
UPPS1510WT....225, 286
UPPS1713BN....225, 301
UPPS1713WT....225, 301
UPPS2813BN....225, 276
UPPS2813WT....225, 276
UPRZ43426C....219, 532
UPRZ53426C....219, 532
UPSE8701WT....226, 320
UPTR1716WT....218, 301
UPTR5007WT....218
UPTR8701IS....218, 320
UPTR8701WT....218, 320
UST1505WT....140, 285
UST1716WT....140, 299
UST5003WT....138, 139
UST6127WT....140, 525

V

VLA1618C....185, 309
VLA2820C....185, 274
VVAM6130BN....511
VVAM6130PN....511
VVAM9362BN....511
VVAM9362PN....511
VVBT6220WT....510
VVBT9348WT....510
VVCS6332OI....510
VVCS9360OI....510
VVCS9556OI....510
VVKY6328BN....509
VVKY6328PN....509
VVKY9258BN....508
VVKY9258PN....508
VVKY9358BN....509
VVKY9358PN....509
VVKY9558BN....508
VVKY9558PN....508
VVKY9658BN....508
VVKY9658PN....508
VVSP9348BN....512
VVSP9348WT....512
VVTH9348AB....512
VVTH9348IB....512
VVWH9348IB....511
VYR5006ML....149
VYR5008ML....149
VYR5012ML....149
VYR5024ML....148

W

WDM5005WT....160, 251
WHI1716IS....100, 299
WHI5005IS....99, 100
WHI5009IS....97
WHI5012IS....96
WHI8701IS....97, 98, 319
WLR1506MB....135, 285
WLR1716MB....135, 299
WLR2820MB....135, 274
WLR5204MB....134
WLS1613PN....307
WLS1615PN....307
WSY5005IF....153
WSY5008IF....153
WSY5012IF....152
WV1716BN....290

Y, Z

YU8710IB....318
ZE1617K....239, 310
ZE1717K....239, 301
ZE2822K....239, 277
ZP8414MD....240, 458
ZP8418MD....240, 458

9006-9112

9006EXAN....534
9006EXBA....534
9006EXBN....534
9006EXC....534
9006EXCC....534
9006EXD....534
9006EXDC....534
9006EXDK....534
9006EXES....534
9006EXIB....534
9006EXIF....534
9006EXIN01....534
9006EXIS....534
9006EXK....534
9006EXK01....534
9006EXLN....534
9006EXMB....534
9006EXMC....534
9006EXML....534
9006EXMM....534
9006EXMN....534
9006EXOS....534
9006EXOZ1....534
9006EXPN....534
9006EXRC....534
9006EXRK....534
9006EXRS....534
9006EXTM....534
9006EXVA....534
9006EXVB....534
9006EXVG....534
9006EXWT....534
9007EXAN....535
9007EXBN01....535
9007EXC....535
9007EXCC....535
9007EXIS....535
9007EXMM....535
9007EXOS....535
9007EXPN....535
9007EXRK....535
9007EXVA....535
9007EXWT....535
9008EXAN....535
9008EXBN01....535
9008EXC....535
9008EXCC....535
9008EXIS....535
9008EXMM....535
9008EXOS....535
9008EXPN....535
9008EXRK....535
9008EXVA....535
9008EXWT....535
9012EXAN....534
9012EXBA....534
9012EXBN....534
9012EXC....534
9012EXCC....534
9012EXD....534
9012EXDC....534
9012EXDK....534
9012EXES....534
9012EXIB....534
9012EXIF....534
9012EXIN01....534
9012EXIS....534
9012EXK....534
9012EXK01....534
9012EXLN....534
9012EXMB....534
9012EXMC....534
9012EXML....534
9012EXMM....534
9012EXMN....534
9012EXOS....534
9012EXOZ1....534
9012EXPN....534
9012EXRC....534
9012EXRK....534
9012EXRS....534
9012EXTB....534
9012EXTM....534
9012EXVA....534
9012EXVB....534
9012EXVG....534
9012EXWT....534
9016EXPN....534
9106EXBN....535
9112EXBN....535

QUOIZEL®

Artisans in Lighting...since 1930

www.quoizel.com

Corporate Headquarters

6 Corporate Parkway, Goose Creek, SC 29445
Phone: (843) 553-6700

Corporate Headquarters/ Customer Service

590 Old Willets Path, Hauppauge, NY 11788
Phone: (631) 273-2700 Fax: (631) 231-7102
Toll-Free Consumer Hotline: 800-645-3184

Showroom – Dallas Trade Mart

3rd Floor, Space 3200, Dallas TX 75207
Phone: (214) 747-3665

Showroom – High Point Market

Showplace 3515
211 E. Commerce Ave., High Point NC 27260

$10.00 CQ2017X
Printed in Canada.

© 2016 Quoizel, Inc.