




Progress Lighting  
701 Millennium Boulevard  
Greenville, South Carolina  
29607  
progresslighting.com



PROGRESS LIGHTING  
**PROGRESS**  
LIGHTING

LED Lighting Solutions



LED Lighting  
Solutions

With more and more homeowners completing renovations in 2014 and the recent phase out of certain light sources, it seems everyone is talking about LED lighting. These energy-efficient sources provide numerous benefits – from energy savings to aesthetic appeal.

Let's start with some of the basics about LED lighting:

**How LEDs work**

to produce light very efficiently. An electrical current passed through semiconductor material illuminates the tiny light sources we call LEDs. The heat produced is absorbed into a heat sink.

**Saving energy with LEDs**

According to the Department of Energy, "LEDs offer the potential for cutting general lighting energy use nearly in half by 2030, saving energy dollars and carbon emissions in the process.

**Expected Life of LEDs**

Good-quality white LEDs in well-designed fixtures are expected to have a useful life of 30,000 to 50,000 hours or longer.

**Measuring color in LEDs**

Color appearance is communicated using correlated color temperature (CCT) on the Kelvin (K) scale. For most interior lighting applications, warm-white (2700K to 3000K) is preferred.

**Inherent benefits of LEDs**

LEDs have many unique, inherent benefits including long life, ease of maintenance, resistance to breakage, lack of infrared or ultraviolet emissions, and instant-on performance.



|                  |    |
|------------------|----|
| CLOSE-TO-CEILING | 2  |
| PENDANTS         | 15 |
| BATH & VANITY    | 19 |
| UNDERCABINET     | 24 |
| SCONCES          | 28 |
| TRACK            | 32 |
| OUTDOOR          | 35 |
| LANDSCAPE        | 54 |
| RECESSED         | 56 |

# Mini Flush Mount

The LED flush mount series uses an intuitive snap-in system that makes flush mount installation easier than ever. Simply, install adapter onto junction box, then snap into place using the flush mount clip.



### FEATURES

- Flicker free dimming with many ELV dimmers
- Wet location listed
- 3000K color temperature
- 90+CRI
- 120v input voltage AC
- TM-21 60,000 hr. life
- 17w: 1035 delivered Lumens, 60 Lumens/watt
- 12w: 630 delivered Lumens, 52.5 Lumens/watt
- 10.5w: 670 delivered Lumens, 63.8 Lumens/watt
- CA Title 24 Compliant

Product No. **P8022-20/30K9-AC1-L10** Antique Bronze  
**P8022-28/30K9-AC1-L10** White  
**P8022-31/30K9-AC1-L10** Black  
**P8022-82/30K9-AC1-L10** Metallic Gray

Description One-light

Size 7-1/4" dia., 1-1/4" ht.

Lamp One 17w LED module included

P8022-20/30K9-AC1-L10



P8022-28/30K9-AC1-L10



P8022-31/30K9-AC1-L10



P8022-82/30K9-AC1-L10



Product No. **P8027-20/30K9-AC1-L10** Antique Bronze  
**P8027-28/30K9-AC1-L10** White  
**P8027-31/30K9-AC1-L10** Black  
**P8027-82/30K9-AC1-L10** Metallic Gray

Description One-light

Size 7-1/4" sq., 1-1/4" ht.

Lamp One 17w LED module included

P8027-20/30K9-AC1-L10



P8027-28/30K9-AC1-L10



P8027-31/30K9-AC1-L10



P8027-82/30K9-AC1-L10



Product No. **P8222-28/30K9-AC1-L10** White

Description One-light flush mount only (no recessed hardware)

Size 7-1/4" sq., 1-1/4" ht.


Lamp One 17w LED module included

P8222-28/30K9-AC1-L10



### EASY INSTALLATION

- 1 Attach snap-in adapter on junction box
- 2 Connect wires
- 3 Snap into place with the flush mount clips



Product No. **P8240-20/30K9-AC1-L06** Antique Bronze  
**P8240-28/30K9-AC1-L06** White  
**P8240-31/30K9-AC1-L06** Black  
**P8240-82/30K9-AC1-L06** Metallic Gray

Description One-light

Size 5-1/2" dia., 1-1/2" ht.

Lamp One 12w LED module included

P8240-20/30K9-AC1-L06



P8240-28/30K9-AC1-L06



P8240-31/30K9-AC1-L06



P8240-82/30K9-AC1-L06



Product No. **P8241-20/30K9-AC1-L06** Antique Bronze  
**P8241-28/30K9-AC1-L06** White  
**P8241-31/30K9-AC1-L06** Black  
**P8241-82/30K9-AC1-L06** Metallic Gray

Description One-light

Size 5-1/4" dia., 1-1/2" ht.

Lamp One 10.5w LED module included

P8241-20/30K9-AC1-L06



P8241-28/30K9-AC1-L06



P8241-31/30K9-AC1-L06



P8241-82/30K9-AC1-L06



Product No. **P8247-09/30K9-AC1-L06** Brushed Nickel  
**P8247-20/30K9-AC1-L06** Antique Bronze  
**P8247-28/30K9-AC1-L06** White  
**P8247-31/30K9-AC1-L06** Black

Description One-light with etched glass diffuser

Size 5-1/2" dia., 1-1/2" ht.

Lamp One 12w LED module included

P8247-09/30K9-AC1-L06



P8247-28/30K9-AC1-L06



P8247-20/30K9-AC1-L06



P8247-31/30K9-AC1-L06



FEATURES

- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

ETCHED OR UMBER GLASS

|  |   |  |
|--|---|--|
| <p>Product No. <b>P2302-0930K9</b> Brushed Nickel<br/><b>P2302-2030K9</b> Antique Bronze</p> <p>Description One-light</p> <p>Size 11" dia., 4" ht.</p> <p>Lamp One 17w LED module included</p> | <p>P2302-0930K9</p>  | <p>P2302-2030K9</p>  |
|--|---|--|

|  |  |   |
|--|--|---|
| <p>Product No. <b>P2303-0930K9</b> Brushed Nickel<br/><b>P2303-2030K9</b> Antique Bronze</p> <p>Description One-light</p> <p>Size 13-1/4" dia., 4-3/4" ht.</p> <p>Lamp One 17w LED module included</p> | <p>P2303-0930K9</p>  | <p>P2303-2030K9</p>  |
|--|--|---|

|   |   |
|---|---|
| <p>Product No. <b>P2321-2030K9</b> Antique Bronze with umber glass</p> <p>Description One-light</p> <p>Size 11 dia., 4" ht.</p> <p>Lamp One 17w LED module included</p> | <p>P2321-2030K9</p>  |
|---|---|

|   |   |
|---|---|
| <p>Product No. <b>P2322-2030K9</b> Antique Bronze with umber glass</p> <p>Description One-light</p> <p>Size 13-1/4 dia., 4-3/4" ht.</p> <p>Lamp One 17w LED module included</p> | <p>P2322-2030K9</p>  |
|---|---|

ETCHED GLASS

|  |   |   |
|--|---|---|
| <p>Product No. <b>P2300-0930K9</b> Brushed Nickel<br/><b>P2300-2030K9</b> Antique Bronze</p> <p>Description One-light</p> <p>Size 11" dia., 4-1/4" ht.</p> <p>Lamp One 17w LED module included</p> | <p>P2300-0930K9</p>  | <p>P2300-2030K9</p>  |
|--|---|---|

|  |   |   |
|--|---|---|
| <p>Product No. <b>P2301-0930K9</b> Brushed Nickel<br/><b>P2301-2030K9</b> Antique Bronze</p> <p>Description One-light</p> <p>Size 12-1/2" dia., 4-1/2" ht.</p> <p>Lamp One 17w LED module included</p> | <p>P2301-0930K9</p>  | <p>P2301-2030K9</p>  |
|--|---|---|

WHITE RIBBED GLASS

|  |  |  |
|--|--|--|
| <p>Product No. <b>P2304-0930K9</b> Brushed Nickel<br/><b>P2304-2030K9</b> Antique Bronze<br/><b>P2304-3030K9</b> White</p> <p>Description One-light</p> <p>Size 11-3/8" dia., 5-3/4" ht.</p> <p>Lamp One 17w LED module included</p> | <p>P2304-0930K9</p>  | <p>P2304-2030K9</p>  |
|--|--|--|

|   |
|---|
| <p>P2304-3030K9</p>  |
|---|

|  |   |   |
|--|---|---|
| <p>Product No. <b>P2305-0930K9</b> Brushed Nickel<br/><b>P2305-2030K9</b> Antique Bronze<br/><b>P2305-3030K9</b> White</p> <p>Description One-light</p> <p>Size 13" dia., 6-3/4" ht.</p> <p>Lamp One 17w LED module included</p> | <p>P2305-0930K9</p>  | <p>P2305-2030K9</p>  |
|--|---|---|

|   |
|---|
| <p>P2305-3030K9</p>  |
|---|

# Helm ADA


**FEATURES**

- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant
- Wall or Ceiling Mount



|             |  |
|-------------|--|
| Product No. | <b>P3447-0930K9</b> Brushed Nickel<br><b>P3447-2030K9</b> Antique Bronze |
| Description | One-light with white acrylic diffuser                                    |
| Size        | 11" sq., 3-3/4" ht.  |
| Lamp        | One 17w LED module included  |

P3447-0930K9



P3447-2030K9



|             |  |
|-------------|--|
| Product No. | <b>P3448-0930K9</b> Brushed Nickel<br><b>P3448-2030K9</b> Antique Bronze |
| Description | Two-light with white acrylic diffuser                                    |
| Size        | 14" sq., 3-3/4" ht.  |
| Lamps       | Two 17w LED modules included   |

P3448-0930K9



P3448-2030K9



|             |  |
|-------------|--|
| Product No. | <b>P3449-0930K9</b> Brushed Nickel<br><b>P3449-2030K9</b> Antique Bronze |
| Description | Three-light with white acrylic diffuser                                  |
| Size        | 18" sq., 3-3/4" ht.  |
| Lamps       | Three 17w LED modules included   |

P3449-0930K9



P3449-2030K9



# Transit ADA

**FEATURES**

- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant
- Wall or Ceiling Mount



|             |  |
|-------------|--|
| Product No. | <b>P3411-0930K9</b> Brushed Nickel<br><b>P3411-2030K9</b> Antique Bronze |
| Description | One-light with white acrylic diffuser                                    |
| Size        | 11" sq., 3-3/4" ht.  |
| Lamp        | One 17w LED module included  |

P3411-0930K9



P3411-2030K9



|             |  |
|-------------|--|
| Product No. | <b>P3417-0930K9</b> Brushed Nickel<br><b>P3417-2030K9</b> Antique Bronze |
| Description | Two-light with white acrylic diffuser                                    |
| Size        | 14" sq., 3-3/4" ht.  |
| Lamps       | Two 17w LED modules included   |

P3417-0930K9



P3417-2030K9



|             |  |
|-------------|--|
| Product No. | <b>P3432-0930K9</b> Brushed Nickel<br><b>P3432-2030K9</b> Antique Bronze |
| Description | Three-light with white acrylic diffuser                                  |
| Size        | 18" sq., 3-3/4" ht.  |
| Lamps       | Three 17w LED modules included   |

P3432-0930K9



P3432-2030K9



FEATURES

- 120v AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant
- Wall or Ceiling Mount

|             |  |
|-------------|--|
| Product No. | <b>P3737-0930K9</b> Brushed Nickel<br><b>P3737-7430K9</b> Venetian Bronze    |
| Description | Five light with distressed mirror surface accents and white acrylic diffuser |
| Size        | 45-3/4" L., 24" W., 3-1/2" ht.   |
| Lamps       | Five 17w LED modules included  |

P3737-0930K9  
shown ceiling-mounted



P3737-7430K9  
shown ceiling-mounted



|             |   |
|-------------|---|
| Product No. | <b>P3747-0930K9</b> Brushed Nickel<br><b>P3747-7430K9</b> Venetian Bronze     |
| Description | Three-light with distressed mirror surface accents and white acrylic diffuser |
| Size        | 24" L., 23-3/4" W., 3-3/8" ht.  |
| Lamps       | Three 17w LED modules included  |

P3747-0930K9  
shown ceiling-mounted



P3747-7430K9  
shown ceiling-mounted



|             |   |
|-------------|---|
| Product No. | <b>P3695-0930K9</b> Brushed Nickel<br><b>P3695-7430K9</b> Venetian Bronze |
| Description | Three-light with white acrylic diffuser                                   |
| Size        | 40" L., 11-5/8" W., 3-3/8" ht.  |
| Lamps       | Three 17w LED modules included  |

P3695-0930K9  
shown ceiling-mounted



P3695-7430K9  
shown ceiling-mounted



|             |   |
|-------------|---|
| Product No. | <b>P3756-0930K9</b> Brushed Nickel<br><b>P3756-7430K9</b> Venetian Bronze   |
| Description | One-light with distressed mirror surface accents and white acrylic diffuser |
| Size        | 18-3/4" dia., 3-3/8" ht.  |
| Lamp        | One 17w LED module included   |

P3756-0930K9  
shown ceiling-mounted



P3756-0930K9  
shown wall-mounted



P3756-7430K9  
shown ceiling-mounted



P3756-7430K9  
shown wall-mounted



# Beyond

**FEATURES**

- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant
- Wall or ceiling mount.

|             |   |
|-------------|---|
| Product No. | <b>P2306-0930K9</b> Brushed Nickel                  |
| Description | One-light with geometric glass and acrylic diffuser |
| Size        | 12" sq., 6" ht.                                     |
| Lamp        | One 17w LED module included                         |

P2306-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P2307-0930K9</b> Brushed Nickel                 |
| Description | One-light with textured glass and acrylic diffuser |
| Size        | 12" dia., 6" ht.                                   |
| Lamp        | One 17w LED module included                        |

P2307-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P2308-0930K9</b> Brushed Nickel   |
| Description | One-light with acrylic diffuser. White, bronze and brushed nickel knobs included |
| Size        | 12" dia., 6" ht.   |
| Lamps       | One 17w LED modules included   |

P2308-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P2309-0930K9</b> Brushed Nickel   |
| Description | One-light with acrylic diffuser. White, bronze and brushed nickel knobs included |
| Size        | 12" sq., 6" ht.  |
| Lamp        | One 17w LED module included  |

P2309-0930K9




|             |  |
|-------------|--|
| Product No. | <b>P2310-0930K9</b> Brushed Nickel                           |
| Description | One-light with etched glass diffuser and brushed metal shade |
| Size        | 10" dia., 5" ht.   |
| Lamps       | One 17w LED modules included                                 |

P2310-0930K9



|             |   |
|-------------|---|
| Product No. | <b>P2311-0930K9</b> Brushed Nickel                              |
| Description | One-light with etched glass diffuser and perforated metal shade |
| Size        | 12" sq., 6" ht.   |
| Lamp        | One 17w LED module included                                     |

P2311-0930K9



# Weaver

**FEATURES**

- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant
- Wall or ceiling mount.

|             |  |
|-------------|--|
| Product No. | <b>P3610-0930K9</b> Brushed Nickel<br><b>P3610-2030K9</b> Antique Bronze     |
| Description | One-light flush mount with linen glass diffuser surrounded by a linen shade. |
| Size        | 10" dia., 3 1/2" ht.   |
| Lamp        | One 17w LED module included  |

P3610-0930K9



P3610-2030K9



|             |  |
|-------------|--|
| Product No. | <b>P3611-0930K9</b> Brushed Nickel<br><b>P3611-2030K9</b> Antique Bronze     |
| Description | Two-light flush mount with linen glass diffuser surrounded by a linen shade. |
| Size        | 16" dia., 4" ht.   |
| Lamps       | Two 17w LED module included  |

P3611-0930K9



P3611-2030K9



|             |  |
|-------------|--|
| Product No. | <b>P3612-0930K9</b> Brushed Nickel<br><b>P3612-2030K9</b> Antique Bronze       |
| Description | Three-light flush mount with linen glass diffuser surrounded by a linen shade. |
| Size        | 22" dia., 3-1/2" ht.   |
| Lamp        | Three 17w LED module included  |

P3612-0930K9



P3612-2030K9



CLOSE-TO-CEILING

FEATURES

- 120V AC Replaceable LED module
- 1211 lumen per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



CLOSE-TO-CEILING

Portal

FEATURES

- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



Maier

|             |   |
|-------------|---|
| Product No. | <b>P3675-0930K9</b> Brushed Nickel<br><b>P3675-2030K9</b> Antique Bronze<br><b>P3675-3030K9</b> White |
| Description | Three-light with white acrylic diffuser   |
| Size        | 18" dia., 5-1/4" ht.  |
| Lamps       | Three 17w LED modules included  |

|             |   |
|-------------|---|
| Product No. | <b>P3910-0930K9</b> Brushed Nickel<br><b>P3910-2030K9</b> Antique Bronze<br><b>P3910-3030K9</b> White |
| Description | One-light with white acrylic diffuser   |
| Size        | 9" dia., 4-3/8" ht.   |
| Lamp        | One 17w LED module included   |

|             |   |
|-------------|---|
| Product No. | <b>P3911-0930K9</b> Brushed Nickel<br><b>P3911-2030K9</b> Antique Bronze<br><b>P3911-3030K9</b> White |
| Description | Two-light with white acrylic diffuser   |
| Size        | 14" dia., 4-3/4" ht.  |
| Lamps       | Two 17w LED modules included  |

P3675-2030K9



P3910-3030K9



P3911-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P3658-0930K9</b> Brushed Nickel<br><b>P3658-2030K9</b> Antique Bronze |
| Description | One-light with white acrylic diffuser                                    |
| Size        | 11" dia., 4-1/8" ht.   |
| Lamp        | One 17w LED module included  |

P3658-0930K9



P3658-2030K9



Round Cloud ADA

6" Fitter

|             |   |
|-------------|---|
| Product No. | <b>P7385-0930K9</b> Brushed Nickel  |
| Description | One-light. Twist on installation. Wall or ceiling mount. White contoured acrylic diffuser with smooth finish texture. |
| Size        | 10-7/8" dia., 3-1/4" ht.  |
| Lamp        | One 17w LED module included   |

|             |   |
|-------------|---|
| Product No. | <b>P3408-0930K9</b> Brushed Nickel<br><b>P3408-2030K9</b> Antique Bronze<br><b>P3408-3030K9</b> White |
| Description | One-light with white opal glass diffuser  |
| Size        | 7-1/2" dia., 4-3/8" ht.   |
| Lamp        | One 17w LED module included   |

P7385-3030K9



P3408-0930K9



P3408-2030K9



P3408-3030K9



|             |  |
|-------------|--|
| Product No. | <b>P3659-0930K9</b> Brushed Nickel<br><b>P3659-2030K9</b> Antique Bronze |
| Description | One-light with white acrylic diffuser                                    |
| Size        | 14" dia., 5-1/4" ht.   |
| Lamp        | One 17w LED module included  |

P3659-0930K9



P3659-2030K9





# Energy Savings



## PENDANTS

### Prismatic Glass



#### FEATURES

- Industrial style metal frame supports clear prismatic glass.
- 120V AC Replaceable LED module
- 623 lumens per module
- 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



With the rapid advancement of lighting technology, LEDs are quickly surpassing the efficiency of more traditional lighting, including fluorescent and incandescent sources. Progress Lighting offers LEDs that meet strict requirements for maximum energy savings and superior performance.

When you select a high-quality LED fixture, you can expect a significant ROI from an energy conservation standpoint.


Here are some of the energy saving benefits of LEDs from Progress Lighting:

**LED sources use** at least 75% less energy than incandescent lighting, allowing homeowners to save on operating expenses.

**LEDs last 35 to 50 times** longer than incandescent sources and approximately 2 to 5 times longer than fluorescent lighting. This means less bulb maintenance.


**LEDs do not produce heat** like traditional sources, reducing cooling costs. Traditional incandescent bulbs waste 98% of the energy they consume on heat.



|             |  |
|-------------|--|
| Product No. | <b>P5075-0930K9</b> Brushed Nickel  |
| Description | One-light mini-pendant with clear prismatic glass and etched diffuser  |
| Size        | 9-1/8" W., 8-1/2" ht. Overall ht. w/stem 74".  |
| Lamp        | One 9w LED module included.  |

P5075-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P5143-0930K9</b> Brushed Nickel  |
| Description | One-light pendant with clear prismatic glass and etched diffuser   |
| Size        | 12-3/4" W., 10-7/8" ht. Overall ht. w/stem 77".  |
| Lamp        | One 9w LED module included.  |

P5143-0930K9



PENDANTS

Fresnel Lens

FEATURES

- Industrial roots in form and function.
- 120V AC Replaceable LED module
- 17w: 1211 lumens, 71.2 lumens per watt
- 9w: 623 lumens, 69.2 lumens per watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

|             |  |
|-------------|--|
| Product No. | <b>P5197-0930K9</b> Brushed Nickel<br><b>P5197-10830K9</b> Oil Rubbed Bronze |
| Description | One-light  |
| Size        | 16" dia., 13-1/4" ht. Overall ht. w/stem 79"; wire 10'.                      |
| Lamp        | One 17w LED module included  |

P5197-0930K9



P5197-10830K9



|             |  |
|-------------|--|
| Product No. | <b>P5188-0930K9</b> Brushed Nickel<br><b>P5188-10830K9</b> Oil Rubbed Bronze |
| Description | One-light  |
| Size        | 12-1/8" dia., 10-1/2" ht. Overall ht. w/stem 77"; wire 10'.                  |
| Lamp        | One 17w LED module included  |

P5188-0930K9



P5188-10830K9



|             |  |
|-------------|--|
| Product No. | <b>P5050-0930K9</b> Brushed Nickel<br><b>P5050-10830K9</b> Oil Rubbed Bronze |
| Description | One-light mini-pendant   |
| Size        | 6-1/8" dia., 6-1/4" ht. Overall ht. w/stem 72-1/4"; wire 10'.                |
| Lamp        | One 9w LED module included   |

P5050-0930K9



P5050-10830K9



PENDANTS

Brookside

FEATURES

- Inspired by vintage light fixtures found in early 20th century train stations.
- 120V AC Replaceable LED module
- 17w: 1211 lumens, 71.2 lumens per watt
- 9w: 623 lumens, 69.2 lumens per watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

|             |  |
|-------------|--|
| Product No. | <b>P5023-0930K9</b> Brushed Nickel<br><b>P5023-2030K9</b> Antique Bronze |
| Description | One-light mini-pendant   |
| Size        | 8" dia., 7-1/2" ht. Overall ht. w/stem 64"; wire 10'.                    |
| Lamp        | One 17w LED module included  |

P5023-0930K9



P5023-2030K9



|             |  |
|-------------|--|
| Product No. | <b>P5024-0930K9</b> Brushed Nickel<br><b>P5024-2030K9</b> Antique Bronze |
| Description | One-light  |
| Size        | 12" dia., 9-1/8" ht. Overall ht. w/stem 65"; wire 15'.                   |
| Lamp        | One 17w LED module included  |

P5024-0930K9



P5024-2030K9



Kiss


|             |   |
|-------------|---|
| Product No. | <b>P5186-0930K9</b> Brushed Nickel          |
| Description | One-light mini-pendant                      |
| Size        | 5" dia., 5-7/8" ht. Overall ht. w/stem 72". |
| Lamp        | One 9w LED module included                  |

P5186-0930K9



|             |   |
|-------------|---|
| Product No. | <b>P5187-0930K9</b> Brushed Nickel            |
| Description | One-light pendant                             |
| Size        | 10" dia., 10-3/4" ht. Overall ht. w/stem 77". |
| Lamp        | One 17w LED module included                   |

P5187-0930K9



PENDANTS

FEATURES

- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



Retro

Retro style LED pendant with prismatic glass

|             |  |
|-------------|--|
| Product No. | <b>P5053-0930K9</b> Brushed Nickel<br><b>P5053-1530K9</b> Polished Chrome<br><b>P5053-7430K9</b> Venetian Bronze |
| Description | One-light  |
| Size        | 14-5/8" dia., 6-5/8" ht. Overall ht. w/stem 73"; wire 15'.   |
| Lamp        | One 17w LED module included  |



Warehouse

Cord hung metal shade with white inner-lining

|             |                                    |
|-------------|------------------------------------|
| Product No. | <b>P5087-0930K9</b> Brushed Nickel |
| Description | One-light mini-pendant             |
| Size        | 10-1/8" dia., 6-1/2" ht. Cord 10'. |
| Lamp        | One 17w LED module included        |

P5087-0930K9



Warehouse

Smooth cord hung metal shade with white inner-lining

|             |  |
|-------------|--|
| Product No. | <b>P5094-0930K9</b> Brushed Nickel<br><b>P5094-3030K9</b> White<br><b>P5094-4530K9</b> Dark Green<br><b>P5094-7430K9</b> Venetian Bronze |
| Description | One-light  |
| Size        | 16" dia., 7-1/2" ht. Overall ht. w/cord 129"; cord 10'.  |
| Lamp        | One 17w LED module included  |



BATH & VANITY

Balance Bath ADA

Frosted white acrylic lens and a Brushed Nickel finish are highlights of these ENERGY STAR fixtures. Wall or ceiling mounted. Can be installed vertically or horizontally.

FEATURES

- 120v AC Replaceable LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- 90+ CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant



|             |   |
|-------------|---|
| Product No. | <b>P2091-0930K9</b> Brushed Nickel      |
| Description | One-light bath                          |
| Size        | 6" W., 5" ht. Extends 3". H/CTR 2-1/2". |
| Lamp        | One 9w LED module included.             |

P2091-0930K9



P2091-0930K9 installed horizontally



|             |  |
|-------------|--|
| Product No. | <b>P2092-0930K9</b> Brushed Nickel           |
| Description | Two-light bath                               |
| Size        | 11-1/2" W., 5" ht. Extends 3". H/CTR 2-1/2". |
| Lamps       | Two 9w LED modules included.                 |

P2092-0930K9



P2092-0930K9 installed horizontally



|             |  |
|-------------|--|
| Product No. | <b>P2093-0930K9</b> Brushed Nickel           |
| Description | Three-light bath                             |
| Size        | 16-3/4" W., 5" ht. Extends 3". H/CTR 2-1/2". |
| Lamps       | Three 9w LED modules included.               |

P2093-0930K9



P2093-0930K9 installed horizontally



|             |  |
|-------------|--|
| Product No. | <b>P2094-0930K9</b> Brushed Nickel       |
| Description | Four-light bath                          |
| Size        | 22" W., 5" ht. Extends 3". H/CTR 2-1/2". |
| Lamps       | Four 9w LED modules included.            |

P2094-0930K9



P2094-0930K9 installed horizontally



FEATURES

- Sleek styling with etched glass
- Dimmable to 10% with many ELV type dimmers
- 120V AC Replaceable LED module
- 623 lumens, 69.2 lumens per watt
- 3000K color temperature
- TM-21 60,000 hr. life
- 90+ CRI
- CA Title 24 Compliant

|             |   |
|-------------|---|
| Product No. | <b>P2142-1530K9</b> Polished Chrome<br><b>P2142-2030K9</b> Antique Bronze |
| Description | One-light bath with etched glass  |
| Size        | 7" W., 4-3/4" ht. Extends 4".<br>H/CTR 2-3/4".                            |
| Lamp        | One 9w LED module included.   |

P2142-1530K9



P2142-2030K9



|             |   |
|-------------|---|
| Product No. | <b>P2143-1530K9</b> Polished Chrome<br><b>P2143-2030K9</b> Antique Bronze |
| Description | Two-light bath with etched glass  |
| Size        | 15-1/2" W., 4-3/4" ht. Extends 4".<br>H/CTR 2-3/8".                       |
| Lamps       | Two 9w LED modules included.  |

P2143-1530K9



P2143-2030K9



|             |   |
|-------------|---|
| Product No. | <b>P2144-1530K9</b> Polished Chrome<br><b>P2144-2030K9</b> Antique Bronze |
| Description | Three-light bath with etched glass  |
| Size        | 24" W., 4-3/4" ht. Extends 4".<br>H/CTR 2-3/8".                           |
| Lamps       | Three 9w LED modules included.  |

P2144-1530K9



P2144-2030K9



|             |   |
|-------------|---|
| Product No. | <b>P2145-1530K9</b> Polished Chrome<br><b>P2145-2030K9</b> Antique Bronze |
| Description | Four-light bath with etched glass   |
| Size        | 32-1/2" W., 4-3/4" ht. Extends 4".<br>H/CTR 2-3/8".                       |
| Lamps       | Four 9w LED modules included.   |

P2145-1530K9



P2145-2030K9



Arch LED is an innovative series of acrylic LED wall sconces that optimizes aesthetic appeal. Frosted white acrylic lens. A perforated metal mesh end cap diffuses light above and below the fixture to provide even illumination.

**FEATURES**

- 120v AC Replaceable LED module
- 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% with many ELV type dimmers
- Wall or ceiling mount
- Can be installed vertically or horizontally



**OPTIONAL SHADE ACCESSORIES**

|             |  |   |
|-------------|--|---|
| Product No. | <b>P2061-0930K9</b> Brushed Nickel         | P2061-0930K9  |
| Description | One-Light Bath                             |  |
| Size        | 7-1/4" W., 6" ht. Extends 3".<br>H/CTR 3". |   |
| Lamp        | One 17w LED module included.               |   |

|             |   |   |
|-------------|---|---|
| Product No. | <b>P2062-0930K9</b> Brushed Nickel          | P2062-0930K9  |
| Description | Two-Light Bath                              |  |
| Size        | 14-1/2" W., 6" ht. Extends 3".<br>H/CTR 3". |   |
| Lamps       | Two 17w LED modules included.               |   |

|             |   |  |
|-------------|---|--|
| Product No. | <b>P2063-0930K9</b> Brushed Nickel          | P2063-0930K9   |
| Description | Three-Light Bath                            |  |
| Size        | 21-3/4" W., 6" ht. Extends 3".<br>H/CTR 3". |  |
| Lamps       | Three 17w LED modules included.             |  |

|             |                                      |  |
|-------------|--------------------------------------|--|
| Product No. | <b>P2064-0930K9</b> Brushed Nickel   | P2064-0930K9   |
| Description | Four-Light Bath                      |  |
| Size        | 29" W., 6" ht. Extends 3". H/CTR 3". |  |
| Lamps       | Four 17w LED modules included.       |  |

|             |   |
|-------------|---|
| Product No. | <b>P8932-01</b> Fabric linen screen print |
| Description | Accessory Shade                           |
| Size        | 6-7/8" W., 6" ht. Extends 2-1/4".         |

P2061-0930K9  
Shown with P8932-01 shade



P2062-0930K9  
Shown with P8932-01 shades



P2063-0930K9  
Shown with P8932-01 shades



|             |                                     |
|-------------|-------------------------------------|
| Product No. | <b>P8934-01</b> Scroll screen print |
| Description | Accessory Shade                     |
| Size        | 6-7/8" W., 6" ht. Extends 2-1/4".   |

P2061-0930K9  
Shown with P8934-01 shade



P2062-0930K9  
Shown with P8934-01 shades



P2064-0930K9  
Shown with P8934-01 shades



## LED Strips

Hide-A-Lite 4 LED Tape lighting for under cabinets and coves. Add aesthetic, energy efficient and functional lighting\* in the most used areas of your home: kitchens, utility rooms, laundry rooms, wet bars, display cases.

### HOW TO USE

Mount securely under cabinets with Hide-a-Lite's durable adhesive backing. Follow four simple steps:

#### 1 Choose a Tape Length

Select LED tape strip length. Hide-a-Lite offers 2"L, 12"L and 60"L size options. Mounting clips are included. (Install in rows of two or more to aid in task lighting or enhance lighting effects.)

#### 2 Select Transformer

Progress Lighting's 24V transformer emits no audible noise, is moisture and shock resistant and employs automatically resetting short circuit protection. Also it is dimmable with an electronic low-voltage dimmer.

#### 3 Use Connectors to Customize Project

Connector cords and L-connectors can increase length and help navigate corners. Choose between a variety of connector cords to allow end-to-end connection.

#### 4 Complete the Look

Select end caps to finish and complete the look.

### 1 Choose a Tape Length

|             |                               |
|-------------|-------------------------------|
| Product No. | <b>P7040-30</b> White         |
| Description | 24V LED 12" 3000K tape light. |
| Size        | 3/8" W., 12" L., 1/8" ht.     |

P7040-30



|             |                              |
|-------------|------------------------------|
| Product No. | <b>P7041-30</b> White        |
| Description | 24V LED 5' 3000K tape light. |
| Size        | 3/8" W., 60" L., 1/8" ht.    |

P7041-30



|             |                              |
|-------------|------------------------------|
| Product No. | <b>P7042-30</b> White        |
| Description | 24V LED 2' 3000K tape light. |
| Size        | 3/8" W., 2' L., 1/8" ht.     |

- 85 CRI, 3000K color temp. 40,000 hr. life
- 120 lumens per foot and consumes 3 watts per foot
- Field cuttable at every 2" to end of run.
- CETL listed damp location

### 2 Select Transformer

|             |                               |
|-------------|-------------------------------|
| Product No. | <b>P8683-31</b> Black         |
| Description | 24V 100w LED tape transformer |
| Size        | 5" L., 2" W., 1" ht.          |

P8683-31



- Hard wire 100w 24V zero load transformer
- High power factor >95%
- Maximum operating temperature -20° C to +90° C
- Electronic circuit design with short circuit and overload protection with auto shut down/reset
- Sound rated A, emits no audible noise
- Integrated 5-pin female connector for direct connection to the 1st LED strip in the run



### 3 Use Connectors to Customize Project

#### CONNECTOR CORDS (optional for joining LED tape between cabinets)

|             |   |
|-------------|---|
| Product No. | <b>P8705-30</b> Black   |
| Description | 8" Connector cord to connect tape sections (P7040, P7041 and P7042) |
| Size        | 72" L., 1/2" W., 3/16" ht.  |

|             |   |
|-------------|---|
| Product No. | <b>P8732-30</b> Black   |
| Description | 6" Connector cord to connect tape sections (P7040, P7041 and P7042) |
| Size        | 6" L., 1/2" W., 3/16" ht.   |

|             |   |
|-------------|---|
| Product No. | <b>P8747-31</b> Black   |
| Description | 2" Connector cord to connect tape sections (P7040, P7041 and P7042) |
| Size        | 2" L., 1/2" W., 3/16" ht.   |

P8705-30



|             |  |
|-------------|--|
| Product No. | <b>P8749-31</b> Black  |
| Description | 12" Connector cord to connect tape sections (P7040, P7041 and P7042) |
| Size        | 12" L., 1/2" W., 3/16" ht.   |

|             |  |
|-------------|--|
| Product No. | <b>P8750-31</b> Black  |
| Description | 18" Connector cord to connect tape sections (P7040, P7041 and P7042) |
| Size        | 18" L., 1/2" W., 3/16" ht.   |

|             |  |
|-------------|--|
| Product No. | <b>P8754-31</b> Black  |
| Description | 36" Connector cord to connect tape sections (P7040, P7041 and P7042) |
| Size        | 18" L., 1/2" W., 3/16" ht.   |

P8732-31



#### L CONNECTOR

|             |  |
|-------------|--|
| Product No. | <b>P8711-30</b> Black  |
| Description | 90° connector for connecting sections of tape (P7040, P7041 and P7042) on corners. |
| Size        | 1-5/16" L., 1-3/8" W.  |

P8711-30



#### Y CONNECTOR

|             |   |
|-------------|---|
| Product No. | <b>P8744-31</b> Black   |
| Description | Three-way Y connector for Hide-a-Lite 4 LED tape (P7040, P7041 and P7042) with 1 male and 2 female connection points. |
| Size        | 4-1/4" dia., 3/16" ht.  |

P8744-31



### 4 Complete the Look

#### MOUNTING CLIPS / END CAPS

|             |   |
|-------------|---|
| Product No. | <b>P8731-30</b> Black   |
| Description | End caps to terminate run of LED tape. Includes one cut end cap and one male end cap. For use when tape has been cut at end of run. |
| Size        | 1/2" L., 1/2" W.  |

P8731-30



|             |  |
|-------------|--|
| Product No. | <b>P8752-01</b>  |
| Description | Pack of 10 clips/screws for straight runs for added support (2 clips per foot recommended) |
| Size        | 1/2" L., 1/2" W.   |

P8752-01



## 120V LED Strips | Undercabinet Systems

Direct Wire and Linkable, with long-life LED's

### Electrical

Each fixture includes 120V dimmable electronic power supplies rated for long-life continuous use. An on/off rocker switch is included.

### Lamping

70% lumen maintenance over 35,000 hours. 3000K, 80+ CRI.

### Construction

Extruded aluminum frame, polycarbonate end plates match frame finish. Tempered micro-prismatic glass lens.

### Linkable

The system can be powered from a single location using the P8740 direct-wire junction box (each fixture can also be direct-wired individually). Using the HAL3 linking cable accessories (P8733-P8743), the fixtures can be linked together to form a continuous row of illumination. (Note: The linking cables can be used with or without the use of the P8740 junction box).

### Dimming

Smooth and continuous dimming on many incandescent dimmer switches (Note: Reference manufacturers' minimum load requirements for dimmer switches). (Except P7002)



Side view showing cable connector

|             |   |  |
|-------------|---|--|
| Product No. | <b>P7002-20</b> Bronze<br><b>P7002-30</b> White |  |
| Description | 120V LED undercabinet. (Non-dimmable)           |  |
| Size        | 3-1/2" W., 9" L., Extends 1".                   |  |
| Lamps       | 4w LED.   |  |



|             |   |  |
|-------------|---|--|
| Product No. | <b>P7012-20</b> Bronze<br><b>P7012-30</b> White |  |
| Description | 120V LED undercabinet.                          |  |
| Size        | 3-1/2" W., 12" L., Extends 1".                  |  |
| Lamps       | 8w LED.   |  |



|             |   |  |
|-------------|---|--|
| Product No. | <b>P7005-20</b> Bronze<br><b>P7005-30</b> White |  |
| Description | 120V LED undercabinet.                          |  |
| Size        | 3-1/2" W., 18" L., Extends 1".                  |  |
| Lamps       | 10w LED.  |  |



|             |   |  |
|-------------|---|--|
| Product No. | <b>P7013-20</b> Bronze<br><b>P7013-30</b> White |  |
| Description | 120V LED undercabinet.                          |  |
| Size        | 3-1/2" W., 24" L., Extends 1".                  |  |
| Lamps       | 14w LED.  |  |



## 120V AC LED Puck

### Electrical

120V AC linkable LED puck. Wet location listed.

### Construction

Die cast enclosure. V5 rated cover and frosted lens.

### Dimmable

Smooth and continuous dimming using most incandescent dimmers (Note: Reference dimmer manufacturer's minimum load requirements.)


### Lamping

Long life LED's 50,000 hours, 70% lumen maintenance. 3000K color temperature, 85+ CRI.

### Linkable


This system can be powered from a single location using the P8740 direct-wire junction box using HAL3 linking cables (P8733, P8735, P8737, P8738). The fixtures can be linked together to form a continuous row of illumination.

|             |                                    |
|-------------|------------------------------------|
| Product No. | <b>P7510-30</b> White              |
| Description | Two-light LED Puck, 120V LED puck. |
| Size        | 3-1/4" dia., 15/16" ht.            |
| Lamps       | 4w LED array.                      |



### HAL 3 JUNCTION BOX


|             |   |
|-------------|---|
| Product No. | <b>P8740-20</b> Antique Bronze<br><b>P8740-30</b> White |
| Description | HAL3 junction box.                                      |
| Size        | 3-1/4" W., 7/8" ht. 3-1/2" L.                           |



Shown P8740-30 with P8737-30

### HAL 3 LINKING CABLES


|             |   |
|-------------|---|
| Product No. | <b>P8733-20</b> Antique Bronze<br><b>P8733-30</b> White |
| Description | 12" Undercabinet fixture linking cable.                 |
| Size        | 3/4" W., 3/8" ht. 12" L.                                |




|             |   |
|-------------|---|
| Product No. | <b>P8735-20</b> Antique Bronze<br><b>P8735-30</b> White |
| Description | 6" Undercabinet fixture linking cable.                  |
| Size        | 3/4" W., 3/8" ht. 6" L.                                 |



|             |   |
|-------------|---|
| Product No. | <b>P8737-20</b> Antique Bronze<br><b>P8737-30</b> White |
| Description | 18" Undercabinet fixture linking cable.                 |
| Size        | 3/4" W., 3/8" ht. 18"L.                                 |



|             |   |
|-------------|---|
| Product No. | <b>P8738-20</b> Antique Bronze<br><b>P8738-30</b> White |
| Description | 24" Undercabinet fixture linking cable.                 |
| Size        | 3/4" W., 3/8" ht. 24" L.                                |



|             |   |
|-------------|---|
| Product No. | <b>P8743-20</b> Antique Bronze<br><b>P8743-30</b> White |
| Description | Coupling cable, Connects two linking cables together.   |
| Size        | 3/4" W., 1/2" ht. 6" L.                                 |



Beyond ADA

The Beyond collection offers a variety of modern designs available in round or square styles, featuring options with textured glass, metal overlays, or geometric acrylic diffusers.

FEATURES

- 120v AC Replaceable LED module
- 1211 lumens, 71.2 lumens/watt
- 3000K color temperature;
- 90+ CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant

|             |   |
|-------------|---|
| Product No. | <b>P2306-0930K9</b> Brushed Nickel        |
| Description | Geometric glass with acrylic diffuser     |
| Size        | 12" W., 12" ht. Extends 2-5/8". H/CTR 6". |
| Lamp        | One 17w LED module included.              |

P2306-0930K9



|             |   |
|-------------|---|
| Product No. | <b>P2307-0930K9</b> Brushed Nickel        |
| Description | Textured glass with acrylic diffuser      |
| Size        | 12" W., 12" ht. Extends 2-5/8". H/CTR 6". |
| Lamp        | One 17w LED module included.              |

P2307-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P2308-0930K9</b> Brushed Nickel                                   |
| Description | Acrylic diffuser. Includes bronze, white and brushed nickel finials. |
| Size        | 12" W., 12" ht. Extends 2-7/8". H/CTR 6".                            |
| Lamp        | One 17w LED module included.   |

P2308-0930K9

*Shown with white finial*

P2308-0930K9

*Shown with bronze finial*



|             |  |
|-------------|--|
| Product No. | <b>P2309-0930K9</b> Brushed Nickel                                   |
| Description | Acrylic diffuser. Includes bronze, white and brushed nickel finials. |
| Size        | 12" W., 12" ht. Extends 3". H/CTR 6".                                |
| Lamp        | One 17w LED module included.   |

P2309-0930K9

*Shown with brushed nickel finial*

P2309-0930K9

*Shown with bronze finial*



|             |   |
|-------------|---|
| Product No. | <b>P2310-0930K9</b> Brushed Nickel        |
| Description | Etched glass with brushed metal shade     |
| Size        | 10" W., 10" ht. Extends 2-1/2". H/CTR 6". |
| Lamp        | One 17w LED module included.              |

P2310-0930K9



|             |   |
|-------------|---|
| Product No. | <b>P2311-0930K9</b> Brushed Nickel        |
| Description | Etched glass with perforated metal shade  |
| Size        | 12" W., 12" ht. Extends 2-7/8". H/CTR 6". |
| Lamp        | One 17w LED module included.              |

P2311-0930K9



FEATURES

- 120V AC Replaceable LED module
- 17w: 1211 lumens, 71.2 lumens per watt
- 9w: 623 lumens, 69.2 lumens per watt
- 90+ CRI

- 3000K color temperature
- Dimmable to 10% with many ELV type dimmers
- Energy Star and CA Title 24 Compliant

Arch ADA

Screen-printed lens accessories – in fabric linen or nature-inspired patterns – can be inserted into the fixtures for a unique effect, while a perforated metal mesh end cap diffuses light above and below for even illumination.

|             |   |
|-------------|---|
| Product No. | <b>P2061-0930K9</b> Brushed Nickel      |
| Description | One-Light Bath                          |
| Size        | 7-1/4" W., 6" ht. Extends 3". H/CTR 3". |
| Lamp        | One 17w LED module included.            |

P2061-0930K9



OPTIONAL SHADE ACCESSORIES

|             |   |
|-------------|---|
| Product No. | <b>P8932-01</b> Fabric linen screen print |
| Description | Accessory Shade                           |
| Size        | 6-7/8" W., 6" ht. Extends 2-1/4".         |

P2061-0930K9

*Shown with P8932-01 shade*



|             |                                     |
|-------------|-------------------------------------|
| Product No. | <b>P8934-01</b> Scroll screen print |
| Description | Accessory Shade                     |
| Size        | 6-7/8" W., 6" ht. Extends 2-1/4".   |

P2061-0930K9

*Shown with P8934-01 shade*



Balance ADA

Soft acrylic lens and a Brushed Nickel finish. Installs vertically or horizontally.

|             |   |
|-------------|---|
| Product No. | <b>P2091-0930K9</b> Brushed Nickel      |
| Size        | 6" W., 5" ht. Extends 3". H/CTR 2-1/2". |
| Lamp        | One 9w LED module included.             |

P2091-0930K9 installed horizontally



P2091-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P2092-0930K9</b> Brushed Nickel           |
| Size        | 11-1/2" W., 5" ht. Extends 3". H/CTR 2-1/2". |
| Lamps       | Two 9w LED modules included.                 |

P2092-0930K9 installed horizontally



P2092-0930K9





# ADA Sconces

**FEATURES**

- 120V AC Replaceable LED module
- 1211 lumens, 71.2 lumens per watt
- 90+ CRI
- TM-21 60,000 hr. life
- 3000K color temperature
- Dimmable to 10% with many ELV type dimmers
- Energy Star and CA Title 24 Compliant
- ADA - Complies with American Disabilities Act



|             |  |
|-------------|--|
| Product No. | <b>P7083-0930K9</b> Brushed Nickel               |
| Description | White Acrylic.                                   |
| Size        | 8-7/8" W., 10-5/8" ht. Extends 4". H/CTR 5-3/8". |
| Lamp        | One 17w LED module included.                     |

P7083-0930K9



|             |   |
|-------------|---|
| Product No. | <b>P7085-0930K9</b> Brushed Nickel                    |
| Description | White Acrylic.  |
| Size        | 9-1/2" W., 10-5/8" ht. Extends 3-3/4". H/CTR 10-3/8". |
| Lamp        | One 17w LED module included.                          |

P7085-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P7088-0930K9</b> Brushed Nickel               |
| Description | White Acrylic.                                   |
| Size        | 8" W., 10-5/8" ht. Extends 3-7/8". H/CTR 5-3/8". |
| Lamp        | One 17w LED module included.                     |

P7088-0930K9



|             |  |
|-------------|--|
| Product No. | <b>P7092-0930K9</b> Brushed Nickel           |
| Description | Etched opal. Enclosed one-piece glass.       |
| Size        | 8" W., 10-3/4" ht. Extends 4". H/CTR 5-1/2". |
| Lamp        | One 17w LED module included.                 |

P7092-0930K9



|             |   |
|-------------|---|
| Product No. | <b>P7093-3030K9</b> White                                       |
| Description | White Glass. Includes bronze, white and brushed nickel finials. |
| Size        | 11-1/4" W., 11-5/16" ht. Extends 3-1/2". H/CTR 3".              |
| Lamp        | One 17w LED module included.                                    |

P7093-3030K9

*Shown with white finial*



P7093-3030K9

*Shown with brushed nickel finial*



P7093-3030K9

*Shown with bronze finial*



# Incorporating LEDs Into Your Home Design



Progress Lighting makes switching to LEDs easy by offering a variety of options – from statement decorative fixtures to subtle accent lights. Here are four ways you can use LED lights in your home.

**Recessed Lighting:** Replacing recessed fixtures with LED sources is an easy way to use LEDs to create beautiful ambient lighting. Check out our previous post on the Basics of Recessed Lighting for tips on choosing and installing recessed fixtures – from sizing to spacing.

**Accent Lighting:** LED sources can add visual interest to any room of the home through accent illumination. Try using an LED step light along a walkway, stairs or on the side of a kitchen island.

**Task Lighting:** Consider adding under cabinet lighting to enhance task or work areas. Progress Lighting's LED under cabinet series, or LED tape light, can be used to brighten kitchen counter spaces and improve functionality.

**Decorative Lighting:** With energy efficiency on the rise, more decorative fixtures have begun to incorporate LED sources. For example, the Progress Lighting Bingo collection comes with replaceable LED modules in a bold and beautiful design.



# LED Track

**FEATURES**

- 120v AC Replaceable LED module
- 6w: 400 lumens
- 9w: 600 lumens
- 90+ CRI
- 3000K color temperature
- Dimmable to 10% with many ELV type dimmers
- LED Track is not compatible with AlphaTrack. Must use LED track accessories with LED track heads<sup>1</sup>

## LED TRACK - 6W<sup>1</sup>

Product No. **P9061-0930K9** Brushed Nickel  
**P9061-2830K9** White  
**P9061-3130K9** Black

Size 3-1/4" dia., 6-3/8" ht.

Lamp One 6w LED included.



Product No. **P9071-0930K9** Brushed Nickel  
**P9071-2830K9** White  
**P9071-3130K9** Black

Size 3" dia., 7" ht.

Lamp One 6w LED included.



Product No. **P9081-2830K9** White  
**P9081-3130K9** Black

Size 2-7/8" dia., 7-1/8" ht.

Lamp One 6w LED included.



## LED TRACK - 9W<sup>1</sup>

Product No. **P9062-0930K9** Brushed Nickel  
**P9062-2830K9** White  
**P9062-3130K9** Black

Size 3-5/8" dia., 7-3/4" ht.

Lamp One 9.3w LED included.



Product No. **P9072-0930K9** Brushed Nickel  
**P9072-2830K9** White  
**P9072-3130K9** Black

Size 2.5" dia., 7-5/8" ht.


Lamp One 9.3w LED included.



Product No. **P9082-2830K9** White  
**P9082-3130K9** Black

Size 3-3/8" dia., 7-1/2" ht.

Lamp One 9.3w LED included.



Note: Height is to bottom of track.

<sup>1</sup> Note: LED Track is not compatible with AlphaTrack. Must use LED track accessories with LED track heads.

# Flex-Track

**FEATURES**


- 400 lumens
- 90+ CRI
- 3000K color temperature
- Dimmable to 10% with many ELV type dimmers
- LED Flex-Track is not compatible with IllumaFlex. Must use Flex-Track accessories with Flex-Track track heads<sup>2</sup>

## LED FLEX-TRACK<sup>2</sup>

Product No. **P9021-0930K9** Brushed Nickel  
**P9021-2030K9** Antique Bronze

Size 2-7/8" dia., 6-1/2" ht.

Lamp One 6w LED module included.




Product No. **P9031-0930K9** Brushed Nickel  
**P9031-2030K9** Antique Bronze

Size 2-1/2" dia., 7" ht.

Lamp One 6w LED module included.



<sup>2</sup> Note: LED Flex-Track is not compatible with IllumaFlex. Must use Flex-Track accessories with Flex-Track track heads.




Note: Height is to bottom of track.

## LED TRACK ACCESSORIES<sup>1</sup>

Product No. **P9054-28** White  
**P9054-31** Black

Description 4' of 120V Straight Track.


Size 1-1/2" W, 1/2" ht., 4' L.



Product No. **P9051-28** White  
**P9051-31** Black

Description Floating Power Canopy

Size 4-1/4" W, 1-1/3" ht.



Product No. **P9052-01**

Description Straight Connector. White with black cap. Can be used with both white and black track.

Size 3/4" W, 1-1/3" ht.



## LED FLEX-TRACK ACCESSORIES<sup>2</sup>

Product No. **P9010-09** Brushed Nickel  
**P9010-20** Antique Bronze

Description 10' of 120V Line Voltage Flexible Track with 5 support stems, end caps, mounting hardware and power feed. Track can be field-cut to desired length.



Size (track): 7/8" H, 6' L.  
 (sppt. stems): 7/8" W, 4-3/4" H.

Product No. **P9001-09** Brushed Nickel  
**P9001-20** Antique Bronze

Description Straight Connector Adapter

Size 1-1/8" W, 7/8" ht.





Outdoor LEDs are very popular due to some key advantages over other light sources. Some of these include:

**Safety:** Because LEDs do not produce an exceptional amount of heat like other landscape and outdoor options, homeowners can be at ease knowing their outdoor LED lights will illuminate their property with minimum fire risk. Additionally, children playing in the yard are not at risk for burns due to the low temperature compared to other light sources that can get very hot.

**Energy:** The energy saving benefits are even more applicable to exterior settings since outdoor lights are often left on for hours at a time.

**Maintenance:** Outdoor lights can be difficult (and time consuming) to replace, especially for lights on a roof. An LED lamp can last up to 20 years, making LEDs an extremely low maintenance solution.

Outdoor LEDs can be used in a variety of ways, including:

**Down Lights:** Shine LED down lights on areas ideal for outdoor entertaining. Recessed LED fixtures create a comfortable environment and add to your home's safety and security.

**Path Lights:** Guide guests along exterior pathways and steps using LED path lights.


**Spotlights:** LED spotlights can be used to highlight architecture, gardens and key focal points of your landscape design. Spotlights also add visual intrigue to exterior areas, boosting curb appeal.


**Wall Lanterns:** Like down lights, LED wall lanterns contribute to the mood of outdoor living areas. Make guests feel at ease in your outdoor space by positioning wall lanterns around popular gathering spaces.


Endorse celebrates the traditional form of a gas-powered coach light with illumination from an LED source. Die-cast aluminum, powder coated frame with clear beveled glass. To add a decorative element, a fluted frosted glass column is offered as an accessory.


**FEATURES**

- 120v AC Replaceable LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- 90+ CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant

|             |   |
|-------------|---|
| Product No. | <b>P6056-3130K9</b> Black  |
| Description | Small Wall Lantern  |
| Size        | 6-3/4" W., 12" ht.<br>Extends 7-5/8".<br>H/CTR 3-1/4".  |
| Lamp        | One 9w LED module included.   |

|             |   |
|-------------|---|
| Product No. | <b>P6057-3130K9</b> Black  |
| Description | Medium Wall Lantern   |
| Size        | 8-3/4" W., 14-3/4" ht.<br>Extends 9-3/4".<br>H/CTR 4".  |
| Lamp        | One 9w LED module included.   |

|             |   |
|-------------|---|
| Product No. | <b>P6058-3130K9</b> Black  |
| Description | Large Wall Lantern  |
| Size        | 10-3/4" W., 17-3/4" ht.<br>Extends 11-3/4".<br>H/CTR 4".  |
| Lamp        | One 9w LED module included.   |

|             |   |
|-------------|---|
| Product No. | <b>P6526-3130K9</b> Black  |
| Description | Hanging Lantern   |
| Size        | 8-3/4" sq., 14-1/2" ht.<br>Overall ht. w/chain 101";<br>wire 180".  |
| Lamp        | One 9w LED module included.   |



**ACCESSORY COLUMNS**

|             |                        |
|-------------|------------------------|
| Product No. | <b>P8774-31</b> Black  |
| Description | For use with P6056     |
| Size        | 2-3/4" sq., 9-5/8" ht. |



|             |                           |
|-------------|---------------------------|
| Product No. | <b>P8775-31</b> Black     |
| Description | For use with P6057, P6526 |
| Size        | 2-3/4" sq., 12-3/8" ht.   |



|             |                         |
|-------------|-------------------------|
| Product No. | <b>P8779-31</b> Black   |
| Description | For use with P6058      |
| Size        | 2-3/4" sq., 15-1/4" ht. |



East Haven LED lanterns feature a die-cast aluminum powder coated frame with clear seeded glass.

FEATURES

- 120v AC Replaceable LED module
- 17w: 1211 lumens, 71.2 lumens/watt
- 9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)

|             |   |
|-------------|---|
| Product No. | <b>P6077-2030K9</b> Antique Bronze<br><b>P6077-3130K9</b> Black |
| Description | Small Wall Lantern  |
| Size        | 5-3/4" W., 7-7/8" ht. Extends 7-1/2".<br>H/CTR 4-3/4".          |
| Lamp        | One 9w LED module included.                                     |

P6077-2030K9



P6077-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6078-2030K9</b> Antique Bronze<br><b>P6078-3130K9</b> Black |
| Description | Medium Wall Lantern   |
| Size        | 7-1/2" W., 9-1/2" ht. Extends 9-1/8".<br>H/CTR 4-3/4".          |
| Lamp        | One 9w LED module included.                                     |

P6078-2030K9



P6078-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6079-2030K9</b> Antique Bronze<br><b>P6079-3130K9</b> Black |
| Description | Large Wall Lantern  |
| Size        | 9-1/2" W., 12" ht. Extends 11-1/8".<br>H/CTR 4-3/4".            |
| Lamp        | One 17w LED module included.                                    |

P6079-2030K9



P6079-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6430-2030K9</b> Antique Bronze<br><b>P6430-3130K9</b> Black |
| Description | Post Lantern  |
| Size        | 7-1/2" W., 15" ht. Fits 3" post<br>(order separately).          |
| Lamp        | One 9w LED module included.                                     |

P6430-2030K9



P6430-3130K9




|             |   |
|-------------|---|
| Product No. | <b>P6530-2030K9</b> Antique Bronze<br><b>P6530-3130K9</b> Black |
| Description | Hanging Lantern   |
| Size        | 7-1/2" W., 10-3/8" ht.<br>Overall ht. w/chain 87".              |
| Lamp        | One 9w LED module included.                                     |

P6530-2030K9




P6530-3130K9



Arrive LED lanterns feature a die-cast aluminum powder coated frame and heavily textured glass.


FEATURES

- 120v AC Replaceable LED module
- 17w: 1211 lumens, 71.2 lumens/watt
- 9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)

|             |   |
|-------------|---|
| Product No. | <b>P6067-3130K9</b> Black  |
| Description | Small Wall Lantern  |
| Size        | 6" W., 8-3/4" ht. Extends 7-3/8" H/CTR 4".  |
| Lamp        | One 9w LED module included.   |


P6067-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6068-3130K9</b> Black  |
| Description | Medium Wall Lantern   |
| Size        | 7-1/2" W., 11-1/8" ht. Extends 8-3/4". H/CTR 5-1/4".  |
| Lamp        | One 9w LED module included.   |


P6068-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6069-3130K9</b> Black  |
| Description | Large Wall Lantern  |
| Size        | 9" W., 13" ht. Extends 10-1/4". H/CTR 5-3/4".   |
| Lamp        | One 17w LED module included.  |


P6069-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6076-3130K9</b> Black  |
| Description | Extra Large Wall Lantern  |
| Size        | 11" W., 16" ht. Extends 12-1/4". H/CTR 8-5/8".  |
| Lamp        | One 17w LED module included.  |


P6076-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6427-3130K9</b> Black  |
| Description | Post Lantern  |
| Size        | 9" sq., 15-7/8" ht. Fits 3" post (order separately).  |
| Lamp        | One 17w LED module included.  |

P6427-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6527-3130K9</b> Black  |
| Description | Hanging Lantern   |
| Size        | 9" sq., 15-1/8" ht. Overall ht. w/ chain 88-1/4"; wire 180".  |
| Lamp        | One 17w LED module included.  |

P6527-3130K9



Wish LED lanterns feature a die-cast aluminum powder coated frame. Antique Bronze features etched amber linen glass. Black features etched white linen glass. Inner directional cylinder for **Dark Sky** compliance (cylinder is removable for traditional lighting).

FEATURES

- 120v AC Replaceable LED module
- 17w: 1211 lumens, 71.2 lumens/watt
- 9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)



|             |   |
|-------------|---|
| Product No. | <b>P6084-2030K9</b> Antique Bronze<br><b>P6084-3130K9</b> Black |
| Description | Medium Wall Lantern   |
| Size        | 7" W., 8-3/4" ht. Extends 8-5/8".<br>H/CTR 3-1/8".              |
| Lamp        | One 9w LED module included.                                     |



P6084-2030K9



P6084-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6085-2030K9</b> Antique Bronze<br><b>P6085-3130K9</b> Black |
| Description | Large Wall Lantern  |
| Size        | 9" W., 12-1/2" ht. Extends 10-1/2".<br>H/CTR 3-1/8".            |
| Lamp        | One 17w LED module included.                                    |



P6085-2030K9



P6085-3130K9



Dark Sky cylinder included



|             |   |
|-------------|---|
| Product No. | <b>P6424-2030K9</b> Antique Bronze<br><b>P6424-3130K9</b> Black |
| Description | Post Lantern (Dark Sky cylinder not included)                   |
| Size        | 9" W., 15-1/4" ht. Fits 3" post (order separately).             |
| Lamp        | One 9w LED module included.                                     |

P6424-2030K9



P6424-3130K9



|             |   |
|-------------|---|
| Product No. | <b>P6524-2030K9</b> Antique Bronze<br><b>P6524-3130K9</b> Black |
| Description | Hanging Lantern   |
| Size        | 9" W., 12-1/2" ht.<br>Overall ht. w/chain 88".                  |
| Lamp        | One 17w LED module included.                                    |

P6524-2030K9



P6524-3130K9




# Brookside

Get inspired from vintage undertones and train station styling with this energy efficient outdoor lantern collection. Available in aluminum with Gilded Iron finish, solid brass with Antique Nickel finish or Solid Copper that ages to a patina finish. Dark Sky compliant.

## FEATURES

- 120v AC Replaceable LED module
- 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant

|             |   |   |
|-------------|---|---|
| Product No. | <b>P5723-1430K9</b> Copper<br><b>P5723-7130K9</b> Gilded Iron<br><b>P5723-8130K9</b> Antique Nickel |  |
| Description | Large Wall Lantern  |   |
| Size        | 12" W., 12-1/4" ht. Extends 13-1/4".<br>H/CTR 6-7/8".   |   |
| Lamp        | One 17w LED module included.  |   |

P5723-1430K9



P5723-7130K9



P5723-8130K9




# Derby

Craftsman styling marries traditional and rustic details. Derby boasts an artistic pattern glass diffuser with a die-cast aluminum, powder coated Antique Bronze frame.


## FEATURES

- 120v AC Replaceable LED module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant

|             |  |   |
|-------------|--|---|
| Product No. | <b>P5749-2030K9</b> Antique Bronze                 |  |
| Description | Small Wall Lantern                                 |   |
| Size        | 6-1/2" W., 8-3/8" ht.<br>Extends 7-3/8". H/CTR 3". |   |
| Lamp        | One 9w LED module included.                        |   |


P5749-2030K9



|             |   |   |
|-------------|---|---|
| Product No. | <b>P5750-2030K9</b> Antique Bronze                      |  |
| Description | Medium Wall Lantern                                     |   |
| Size        | 8-1/2" W., 11-1/4" ht.<br>Extends 9-3/8". H/CTR 4-1/4". |   |
| Lamp        | One 9w LED module included.                             |   |


P5750-2030K9




|             |   |   |
|-------------|---|---|
| Product No. | <b>P5751-2030K9</b> Antique Bronze                        |  |
| Description | Large Wall Lantern  |   |
| Size        | 10-5/8" W., 15-1/2" ht.<br>Extends 11-5/8". H/CTR 3-3/8". |   |
| Lamp        | One 9w LED module included.                               |   |

P5751-2030K9



|             |                                    |   |
|-------------|------------------------------------|---|
| Product No. | <b>P6017-2030K9</b> Antique Bronze |  |
| Description | Flush Mount                        |   |
| Size        | 10" sq., 5-1/2" ht.                |   |
| Lamp        | One 17w LED module included.       |   |

P6017-2030K9



Westport LED offers traditional styling to complement a variety of home décor options. A durable, die-cast aluminum frame cradles a softly diffused, seeded glass shade

FEATURES

- 120v AC Replaceable LED module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)

Product No. **P5862-2030K9** Antique Bronze  
**P5862-3030K9** White  
**P5862-3130K9** Black

Description Small Wall Lantern

Size 6-7/8" W., 10-1/4" ht.  
 Extends 8-3/8". H/CTR 3-1/8".

Lamp One 9w LED module included.

P5862-2030K9



P5862-3030K9



Product No. **P5863-2030K9** Antique Bronze  
**P5863-3030K9** White  
**P5863-3130K9** Black

Description Medium Wall Lantern

Size 9" W., 12-7/8" ht.  
 Extends 10-3/8". H/CTR 3-3/4".

Lamp One 9w LED module included.

P5863-2030K9



P5863-3130K9



Product No. **P5864-2030K9** Antique Bronze  
**P5864-3030K9** White  
**P5864-3130K9** Black

Description Large Wall Lantern

Size 11" W., 15-3/8" ht.  
 Extends 12-7/8". H/CTR 4".

Lamp One 17w LED module included.

P5864-2030K9



P5864-3130K9



Product No. **P3883-2030K9** Antique Bronze  
**P3883-3030K9** White  
**P3883-3130K9** Black

Description Flush Mount

Size 9" dia., 7-1/4" ht.

Lamp One 17w LED module included.

P3883-2030K9



P3883-3130K9



Product No. **P5445-2030K9** Antique Bronze  
**P5445-3030K9** White  
**P5445-3130K9** Black

Description Post Lantern

Size 9" dia., 16-3/8" ht. Fits 3" post  
 (order separately).

Lamp One 9w LED module included.

P5445-2030K9



P5445-3130K9



Product No. **P5530-2030K9** Antique Bronze  
**P5530-3030K9** White  
**P5530-3130K9** Black

Description Hanging Lantern

Size 9" dia., 11-3/4" ht. Overall ht.  
 w/chain 88"; wire 180".

Lamp One 9w LED module included.

P5530-3030K9



P5530-3130K9





# Aluminum Cylinders

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing, Fade and chip-resistant. UL listed for wet locations when used with lens cover.

## FEATURES

- 120v AC
- 1000 lumens (17w)  
2000 lumens (29w)
- 3000K color temperature
- 90+ CRI
- Dimmable to 10% with many ELV type dimmers

### 6" ALUMINUM CYLINDERS

Product No. **P5641-20/30K** Bronze  
**P5641-30/30K** White  
**P5641-31/30K** Black  
**P5641-82/30K** Metallic Gray

---

Description One-light down (dark sky).

---

Size 6" W., 12" ht. Extends 8-7/8".  
H/CTR 4-1/2".

---

Lamp(s) One 29w LED module included.

P5641-30/30K



P5641-31/30K



P5641-82/30K



Product No. **P5642-20/30K** Bronze  
**P5642-30/30K** White  
**P5642-31/30K** Black  
**P5642-82/30K** Metallic Gray

---

Description Two-light up/down. For wet location specify P8798 top cover lens.

---

Size 6" W., 18" ht. Extends 8-7/8".  
H/CTR 8".

---

Lamp(s) Two 29w LED modules included.

P5642-20/30K



P5642-30/30K



P5642-82/30K



Product No. **P5741-20/30K** Bronze  
**P5741-30/30K** White  
**P5741-31/30K** Black

---

Description One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit (pg. 48).

---

Size 6" dia., 12" ht.

---

Lamp(s) Two 29w LED module included.

P5741-20/30K



P5741-30/30K



P5741-31/30K



### 5" ALUMINUM CYLINDERS

Product No. **P5674-20/30K** Bronze  
**P5674-30/30K** White  
**P5674-31/30K** Black  
**P5674-82/30K** Metallic Gray

---

Description One-light down (dark sky).

---

Size 5" W., 7-1/4" ht. Extends 8".  
H/CTR 2-1/2".

---

Lamp One 17w LED module included.

P5674-82/30K



P5674-20/30K



P5674-30/30K



Product No. **P5675-20/30K** Bronze  
**P5675-30/30K** White  
**P5675-31/30K** Black  
**P5675-82/30K** Metallic Gray

---

Description Two-light up/down. For wet locations specify P8799 top cover lens.

---

Size 5" W., 14" ht. Extends 8". H/CTR 7".

---

Lamps Two 17w LED modules included.

P5675-82/30K



P5675-20/30K



P5675-31/30K



Product No. **P5774-20/30K** Bronze  
**P5774-30/30K** White  
**P5774-31/30K** Black

---

Description One-light. Mounts flush to ceiling (dark sky).

---

Size 5" dia., 6-1/2" ht.

---

Lamp One 17w LED module included.

P5774-20/30K



P5774-30/30K



P5774-31/30K



# Aluminum Cylinders

Product No. **P8710-31** Black anodized aluminum

Description Black Deep groove step baffle to minimize glare for P5641, P5642 and P5741 6" cylinders.

Size 6" dia., 4" ht.

P8710-31



Product No. **P8798-31** Black

Description Top cover lens adapts up/down 6" cylinder, P5642, for wet location use. Heat & shatter-resistant clear tempered lens w/black trim.

Size 6" dia.

P8798-31



Product No. **P8799-30** White  
**P8799-31** Black

Description Top cover lens adapts up/down 5" cylinder, P5675, for wet location use. Heat & shatter-resistant clear tempered lens w/white or black trim.

Size 5" dia.


P8799-31



Product No. **P8741-20** Bronze  
**P8741-30** White  
**P8741-31** Black

Description Pendant kit adapts P5741 ceiling fixture to 6", 12" or 18" stem mounting. Includes canopy, hang-straight swivel, 6" and 12" sections with coupling.

P8741-30




Product No. **P8712-30** White  
**P8712-31** Black

Description Accessory provides additional shielding of the light source to achieve "turtle-friendly" illumination. **Check with your local turtle enforcement official.**

Size 5" dia., 4" ht.

P8712-30

P8712-31



# Posts & Accessories

Surround your home with decorative posts to add style and elegance for years to come, Aluminum construction and popular finish choices add to functionality of outdoor lighting.

## POSTS

Product No. **P5390-20** Antique Bronze  
**P5390-31** Black

Description Aluminum post.

Size 3" dia., 7' ht. (Can be cut to desired length)

P5390-20



Product No. **P5391-20PC** Antique Bronze  
**P5391-31PC** Black

Description Aluminum post with ladder rest and photocell which automatically turns lantern on at dusk and off at dawn.

Size 3" dia., 7' ht. (Can be cut to desired length)

P5391-20PC



Product No. **P5390-31PC** Black

Description Aluminum post with photocell which automatically turns on at dusk, off at dawn.

Size 3" dia., 7' ht. (Can be cut to desired length)

P5390-31PC



Product No. **P5392-31PC** Black

Description Black aluminum post with ladder rest, photocell which automatically turns on at dusk off at dawn and weather proof GCO.

Size 3" dia., 7' ht. (Can be cut to desired length)

P5392-31PC



Product No. **P5391-30** White  
**P5391-31** Black

Description Aluminum post with ladder rest.

Size 3" dia., 7' ht. (Can be cut to desired length)

P5391-30



Product No. **P5394-20** Antique Bronze  
**P5394-31** Black

Description Commercial grade black aluminum post, .125 wall thickness.

Size 3" dia., 12' ht. (Can be cut to desired length)

P5394-20



## POST ACCESSORIES

Aluminum construction offers virtually maintenance-free benefits and sturdy operation that will last over time.

Product No. **P8726-20** Antique Bronze  
**P8726-31** Black  
**P8726-46** Weathered Bronze

Description Cast aluminum pedestal mount. For mounting post lanterns with 3" fitters on pedestals or on top of walls.

Size 7" dia., 3-1/4" ht.

P8726-20

P8726-31

P8726-46



Product No. **P8748-31** Black

Description Surface Mount Post Adapter. Flanged cast aluminum base for surface mounting round 3" bottom O.D. posts. Anchor bolts and allen set screws included.

Size 8" dia., 5" ht.

P8748-31



# Bulkheads

Die-cast aluminum frame with polycarbonate diffuser. Safety listed for wet locations. Wall or ceiling mount.









### FEATURES

- 120v AC Replaceable LED module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)


|             |  |   |  |   |
|-------------|--|---|--|---|
| Product No. | <b>P3647-3030K9</b> White<br><b>P3647-3130K9</b> Black | P3647-3030K9  | <i>Shown as wall mount</i>   | P3647-3130K9  |
| Description | One-light wall or close-to-ceiling                     |  |  |  |
| Size        | 6-1/2" W., 10-1/2" ht.<br>Extends 4-3/8". H/CTR 5-14". |   |  |   |
| Lamp        | One 9w LED module included.                            |   |  |   |

|             |  |   |   |   |
|-------------|--|---|---|---|
| Product No. | <b>P3649-3030K9</b> White<br><b>P3649-3130K9</b> Black | P3649-3030K9  | P3649-3130K9  | <i>Shown as wall mount</i>  |
| Description | One-light wall or close-to-ceiling                     |  |  |  |
| Size        | 6-1/2" W., 10-1/2" ht.<br>Extends 4-1/2". H/CTR 5-14". |   |   |   |
| Lamp        | One 9w LED module included.                            |   |   |   |

|             |  |  |   |  |
|-------------|--|--|---|--|
| Product No. | <b>P3648-3030K9</b> White<br><b>P3648-3130K9</b> Black | P3648-3030K9   | P3648-3130K9  | <i>Shown as wall mount</i>   |
| Description | One-light round wall or close-to-ceiling               |  |  |  |
| Size        | 9-1/2" W., 4-3/8" ht. Extends 4-3/8".<br>H/CTR 4-3/4". |  |   |  |
| Lamp        | One 17w LED module included.                           |  |   |  |

|             |  |  |  |  |
|-------------|--|--|--|--|
| Product No. | <b>P3650-3030K9</b> White<br><b>P3650-3130K9</b> Black | P3650-3030K9   | <i>Shown as wall mount</i>   | P3650-3130K9   |
| Description | One-light round wall or close-to-ceiling               |  |  |  |
| Size        | 9-1/2" W., 4-3/8" ht. Extends 4-1/2".<br>H/CTR 4-3/4". |  |  |  |
| Lamp        | One 17w LED module included.                           |  |  |  |

# Wall Pack

|             |  |  |
|-------------|--|--|
| Product No. | <b>PHSL-13-23-B</b> Antique Bronze   | PHSL-13-23-B   |
| Description | Die-cast aluminum housing with tempered, impact resistant clear glass lens. 23.3w input power. 1184 lumens. 120V/277V driver. 5000K color temperature. |  |
| Size        | 12-3/4" W., 6-3/4" ht. Extends 7-1/4".   |  |
| Lamp        | One 23w LED module included.   |  |

# Non-Metallic

|             |   |   |
|-------------|---|---|
| Product No. | <b>P3715-31</b> Black   | P3715-31  |
| Description | 120V/277V input voltage. Durable non-corrosive UV resistant housing. 4000K, 912 lumens. 74+ CRI. Wet location listed. |  |
| Size        | 6" W., 9" ht. H/CTR 4-1/4".   |   |
| Lamp        | LED array 10w.  |   |



# Step Lights

LED step/wall lights are available in a vertical or horizontal configuration for mounting into a single-gang wallbox. The design is made of heavy steel. Available in louvered or hood design.

## FEATURES

- 120v AC Replaceable LED module
- 100 lumens, 25 lumens/watt (P6827/P6828)
- 84 lumens, 21 lumens/watt (P6829)
- 65 lumens, 16 lumens/watt (P6832)
- 3000K color temperature
- 84+ CRI
- Dimmable to 10% with many ELV type dimmers
- Wet location listed
- TM-21 50,000 hr. life



|             |  |  |   |
|-------------|--|--|---|
| Product No. | <b>P6827-0930K</b> Brushed Nickel<br><b>P6827-2030K</b> Antique Bronze<br><b>P6827-3030K</b> White<br><b>P6827-3130K</b> Black | P6827-0930K  | P6827-3030K   |
| Description | Louvered horizontal step/wall light. Wet location listed.  |  |  |
| Size        | 5-1/4" W. , 3-1/2" ht.   |  |   |
| Lamp        | 4w LED module included.  |  |   |

|   |  |
|---|--|
| P6827-2030K   | P6827-3130K  |
|  |  |

|             |  |  |   |
|-------------|--|--|---|
| Product No. | <b>P6828-0930K</b> Brushed Nickel<br><b>P6828-2030K</b> Antique Bronze<br><b>P6828-3030K</b> White<br><b>P6828-3130K</b> Black | P6828-0930K  | P6828-3030K   |
| Description | Louvered vertical step/wall light. Wet location listed.  |  |  |
| Size        | 3-1/2" W. , 5-1/4" ht.   |  |   |
| Lamp        | 4w LED module included.  |  |   |

|  |   |
|--|---|
| P6828-2030K  | P6828-3130K   |
|  |  |

|             |  |   |   |
|-------------|--|---|---|
| Product No. | <b>P6829-0930K</b> Brushed Nickel<br><b>P6829-2030K</b> Antique Bronze<br><b>P6829-3030K</b> White<br><b>P6829-3130K</b> Black | P6829-0930K   | P6829-3030K   |
| Description | Horizontal step/wall light. Wet location listed.   |  |  |
| Size        | 2-7/8" W., 4-1/2" ht.  |   |   |
| Lamp        | 4w LED module included.  |   |   |

|  |  |
|--|--|
| P6829-2030K  | P6829-3130K  |
|  |  |

|             |  |   |   |
|-------------|--|---|---|
| Product No. | <b>P6832-0930K</b> Brushed Nickel<br><b>P6832-2030K</b> Antique Bronze<br><b>P6832-3030K</b> White<br><b>P6832-3130K</b> Black | P6832-0930K   | P6832-3030K   |
| Description | Vertical step/wall light. Wet location listed.   |  |  |
| Size        | 2-7/8" ht., 4-1/2" W.  |   |   |
| Lamp        | 4w LED module included.  |   |   |

|   |   |
|---|---|
| P6832-2030K   | P6832-3130K   |
|  |  |

Variety of LED landscape lighting options for popular exterior applications. Low voltage LED landscape, bollard and path lights enhance outdoor settings, while adding safety, security and curb appeal to areas around the home. 3000K color temperature.

### FEATURES

- Low voltage system must be used with P8270 transformer
- All paths lights include stake and deck mount, 4ft cable and connector.
- Die cast aluminum construction with powder coat finish
- 3000K color temperature
- 80+ CRI
- Wet location listed

|             |  |
|-------------|--|
| Product No. | <b>P5245-20</b> Antique Bronze<br><b>P5245-31</b> Black            |
| Description | Path light. Includes stake and deck mount, 4' cable and connector. |
| Size        | 6-1/2" dia., 20-3/4" ht. Extends 9-1/2".                           |
| Lamp        | One 1.5w LED module included.                                      |



|             |  |
|-------------|--|
| Product No. | <b>P5247-09</b> Brushed Nickel<br><b>P5247-31</b> Black              |
| Description | Slim bollard. Frosted internal diffuser surrounded by clear plastic. |
| Size        | 2-5/8" dia., 24" ht.   |
| Lamp        | One 1.5w LED module included.  |



|             |  |
|-------------|--|
| Product No. | <b>P5297-31</b> Black  |
| Description | Spread light. Includes stake and deck mount, 4' cable and connector. |
| Size        | 7" dia., 16-1/2" ht.   |
| Lamp        | One 1.5w LED module included.  |



|             |  |
|-------------|--|
| Product No. | <b>P5298-31</b> Black  |
| Description | Path light. Includes stake and deck mount, 4' cable and connector. |
| Size        | 6" dia., 17-1/2" ht.   |
| Lamp        | One 1.5w LED module included.                                      |



### LINEAR PATH LIGHT

|             |  |
|-------------|--|
| Product No. | <b>P5246-31</b> Black  |
| Description | Linear path light with ground stake. Die cast aluminum construction with louvered glass. |
| Size        | 5-3/8" W., 2-5/8" ht.  |
| Lamp        | One 1.5w LED module included.  |



### DECK/RAIL LIGHT

|             |  |
|-------------|--|
| Product No. | <b>P5296-31</b> Black                        |
| Description | Deck/rail light with polycarbonate diffuser. |
| Size        | 4" dia., 2" ht. Extends 3".                  |
| Lamps       | Three 1.5w LED modules included.             |



### WELL LIGHT

|             |  |
|-------------|--|
| Product No. | <b>P5295-31</b> Black  |
| Description | Well light with die cast aluminum, glass cover. Includes 4' cable and connector. |
| Size        | 5" dia., 4" ht.  |
| Lamp        | One 3w LED module included.  |



### FLOOD LIGHT

|             |                                |
|-------------|--------------------------------|
| Product No. | <b>P5299-31</b> Black          |
| Description | Adjustable knuckle for aiming. |
| Size        | 4-1/2" dia., 6-5/8" ht.        |
| Lamp        | One 3w LED module included.    |



### LED TRANSFORMER

|             |  |
|-------------|--|
| Product No. | <b>P8270-31</b> Black  |
| Description | 45w LED Transformer. Non metallic case protects timer controls and 120v to 12v transformer. Surge protected with grounded cord/plug set and easy 12V cable attachment. Photocontrol triggers "time on", eliminating seasonal adjustment. 45w max. Non-dimmable. Recommend using 14 gauge cable (P8716 or P8626). |
| Size        | 4" x 5-5/8" x 3-1/2"   |



### LED 14 GAUGE CABLE

|             |   |
|-------------|---|
| Product No. | <b>P8617-31</b> & <b>P8626-31</b> Black   |
| Description | Low voltage cable. Recommended for use with P8270-31 transformer and LED Lighting. Low voltage #14 cable runs from P8270-31 control center down path of lighting. UV protected, burial is not required, hide with mulch if desired. Perfect fit with fixture connectors for easy installation (150' is the max. run distance from transformer location to assure best fixture operation). |
| Size        | <b>P8617-31</b> 14-gauge 75 ft.<br><b>P8626-31</b> 14-gauge 150 ft.   |



The LED flush mount series uses an intuitive snap-in system that makes flush mount installation easier than ever. Simply, install adapter onto junction box, then snap into place using the flush mount clip.

FEATURES


- Flicker free dimming with many ELV dimmers
- Wet location listed
- 3000K color temperature
- 90+CRI
- 120v input voltage AC
- TM-21 60,000 hr. life
- 17w: 1035 delivered Lumens, 60 Lumens/watt
- 12w: 630 delivered Lumens, 52.5 Lumens/watt
- 10.5w: 670 delivered Lumens, 63.8 Lumens/watt
- CA Title 24 Compliant

SURFACE and RECESSED MOUNT

|             |   |   |  |
|-------------|---|---|--|
| Product No. | <b>P8022-20/30K9-AC1-L10</b> Antique Bronze<br><b>P8022-28/30K9-AC1-L10</b> White<br><b>P8022-31/30K9-AC1-L10</b> Black<br><b>P8022-82/30K9-AC1-L10</b> Metallic Gray |    |    |
| Description | One-light   |   |  |
| Size        | 7-1/4" dia., 1-1/4" ht.   |   |  |
| Lamp        | One 17w LED module included   |   |  |
| Product No. | <b>P8022-31/30K9-AC1-L10</b><br><b>P8022-82/30K9-AC1-L10</b>  |    |    |
| <hr/>       |   |   |  |
| Product No. | <b>P8027-20/30K9-AC1-L10</b> Antique Bronze<br><b>P8027-28/30K9-AC1-L10</b> White<br><b>P8027-31/30K9-AC1-L10</b> Black<br><b>P8027-82/30K9-AC1-L10</b> Metallic Gray |  |  |
| Description | One-light   |   |  |
| Size        | 7-1/4" sq., 1-1/4" ht.  |   |  |
| Lamp        | One 17w LED module included   |   |  |
| Product No. | <b>P8027-31/30K9-AC1-L10</b><br><b>P8027-82/30K9-AC1-L10</b>  |  |  |

SURFACE and RECESSED INSTALLATION HARDWARE

Included adjustable mounting option that fits 6", 5" or 4" recessed housing. The fixture also includes an E26 Edison Base adapter for a retrofit screw-in option. This hardware is included in **P8022** and **P8027** series.



SURFACE MOUNT ONLY

|             |  |   |   |   |   |
|-------------|--|---|---|---|---|
| Product No. | <b>P8240-20/30K9-AC1-L06</b> Antique Bronze<br><b>P8240-28/30K9-AC1-L06</b> White<br><b>P8240-31/30K9-AC1-L06</b> Black<br><b>P8240-82/30K9-AC1-L06</b> Metallic Gray  |    |    |    |    |
| Description | One-light  |   |   |   |   |
| Size        | 5-1/2" dia., 1-1/2" ht.  |   |   |   |   |
| Lamp        | One 12w LED module included  |   |   |   |   |
| Product No. | <b>P8241-20/30K9-AC1-L06</b> Antique Bronze<br><b>P8241-28/30K9-AC1-L06</b> White<br><b>P8241-31/30K9-AC1-L06</b> Black<br><b>P8241-82/30K9-AC1-L06</b> Metallic Gray  |   |   |   |   |
| Description | One-light  |   |   |   |   |
| Size        | 5-1/4" dia., 1-1/2" ht.  |   |   |   |   |
| Lamp        | One 10.5w LED module included  |   |   |   |   |
| Product No. | <b>P8247-09/30K9-AC1-L06</b> Brushed Nickel<br><b>P8247-20/30K9-AC1-L06</b> Antique Bronze<br><b>P8247-28/30K9-AC1-L06</b> White<br><b>P8247-31/30K9-AC1-L06</b> Black |  |  |  |  |
| Description | One-light with etched glass diffuser   |   |   |   |   |
| Size        | 5-1/2" dia., 1-1/2" ht.  |   |   |   |   |
| Lamp        | One 12w LED module included  |   |   |   |   |

RECESSED ADAPTERS

|             |  |
|-------------|--|
| Product No. | <b>P8595-01</b>  |
| Description | Hardware for <b>P8222</b> to make it available for recessed installation. Mounting option fits 6", 5" or 4" recessed housings. Edison base adapter included. |
| Size        | 5-3/16" w, 3-9/16" ht.   |



|             |  |
|-------------|--|
| Product No. | <b>P8596-01</b>  |
| Description | Recessed mounting accessory for <b>P8240</b> , <b>P8241</b> and <b>P8247</b> series. Allows for installation in 4" housings. Edison base adapter included. |



RECESSED

6"

6" NEW CONSTRUCTION HOUSING


|                 |   |
|-----------------|---|
| Product No.     | <b>P87-LED</b>  |
| Description     | New Construction Air-Tight IC and Non-IC. Integral quick connect mates with P8071 series LED trims. |
| Ceiling opening | 6-7/8" dia.   |
| Plaster frame   | 7-7/8" x 10-3/4"  |
| Recessed depth  | 7-1/2"  |
| Pryouts         | 1/2" & 3/4"   |



6" NEW CONSTRUCTION or REMODEL TRIMS

|             |   |
|-------------|---|
| Product No. | <b>P8071-20/30K9-AC1-L07</b> Antique Bronze<br><b>P8071-28/30K9-AC1-L07</b> White<br><b>P8071-31/30K9-AC1-L07</b> Black<br><b>P8071-82/30K9-AC1-L07</b> Metallic Gray |
|-------------|---|

Description 700 lumen 3000K



FEATURES


- Frosted polycarbonate lens controls direct glare from the LEDs
- Dimmable to 10% with many ELV type dimmers
- 12-watt input power
- Lumen output 700 lumens
- Lumen output and distribution comparable to a 65w BR30 incandescent lamp
- 3000K color temperature
- 90+ CRI
- TM-21 60,000 hours life
- Suitable for use in IC or NON-IC applications
- CSAus listed for wet locations

|             |                                    |
|-------------|------------------------------------|
| Product No. | <b>P8071-28/30K-L10-STR2</b> White |
|-------------|------------------------------------|

Description 1000 lumen 3000K

|             |                                    |
|-------------|------------------------------------|
| Product No. | <b>P8071-28/35K-L10-STR2</b> White |
|-------------|------------------------------------|

Description 1000 lumen 3500K



FEATURES


- Frosted polycarbonate lens controls direct glare from the LEDs
- Dimmable to 10% with many ELV type dimmers
- 12-watt input power
- Lumen output 1037 lumens
- Lumen output and distribution comparable to a 75w PAR30 incandescent lamp
- 80+ CRI
- TM-21 60,000 hours life
- Suitable for use in IC or NON-IC applications
- Available in 3000K and 3500K color temperatures
- cULus listed for wet locations

RECESSED


4" & 5"

4" NEW CONSTRUCTION or REMODEL HOUSING

|                 |  |
|-----------------|--|
| Product No.     | <b>P831-LED</b>  |
| Description     | New Construction Air-Tight, IC and Non-IC. Integral quick connect mates with P8080 series LED trims. |
| Ceiling opening | 4-1/2"   |
| Plaster frame   | 8-3/8" x 13"   |
| Recessed depth  | 7-1/2"   |



|                 |   |
|-----------------|---|
| Product No.     | <b>P830-LED</b>   |
| Description     | New Construction Non-IC. Integral quick connect mates with P8080 series LED trims |
| Ceiling opening | 4-1/2"  |
| Plaster frame   | 7-7/8" x 10-3/4"  |
| Recessed depth  | 5-1/2"  |
| Pryouts         | 1/2" and 3/4"   |




|                 |  |
|-----------------|--|
| Product No.     | <b>P832-LED</b>  |
| Description     | Remodel Non-IC. Retrofit version of P830-TG for use in existing ceilings |
| Ceiling opening | 4-1/4"   |
| Recessed depth  | 5-1/2"   |
| Pryouts         | 1/2"   |



4" NEW CONSTRUCTION or REMODEL TRIMS

|             |   |
|-------------|---|
| Product No. | <b>P8080-20/30K9-AC1-L06</b> Antique Bronze<br><b>P8080-28/30K9-AC1-L06</b> White<br><b>P8080-31/30K9-AC1-L06</b> Black<br><b>P8080-82/30K9-AC1-L06</b> Metallic Gray |
|-------------|---|

Description 600 lumen 3000K





FEATURES

- LED (Light Emitting Diode) lamp included
- 10-watt input power
- Lumen output 620 lumens
- Lumen output and distribution comparable to 50w R20 incandescent lamp
- 90+ CRI
- TM-21 60,000 hours life
- Suitable for use in IC or NON-IC applications
- cULus listed for wet locations

5" P8061 NEW CONSTRUCTION or REMODEL (TRIMS ONLY)

|             |   |
|-------------|---|
| Product No. | <b>P8061-20/30K9-AC1-L06</b> Antique Bronze<br><b>P8061-28/30K9-AC1-L06</b> White<br><b>P8061-31/30K9-AC1-L06</b> Black<br><b>P8061-82/30K9-AC1-L06</b> Metallic Gray |
|-------------|---|

Description 600 lumen 3000K



FEATURES

- LED (Light Emitting Diode) lamp included
- Dimmable to 10% with many ELV type dimmers
- 12-watt input power
- Lumen output 635 lumens
- Lumen output and distribution comparable to 65w BR30 incandescent lamp
- 90+ CRI
- TM-21 60,000 hours life
- Suitable for use in IC or NON-IC applications
- cULus listed for wet locations


RECESSED

## 4" Pro-Optic®

### 4" NEW CONSTRUCTION HOUSING

|                   |                   |
|-------------------|-------------------|
| Product No.       | <b>P8064-EBG4</b> |
| Ceiling Opening   | 5-3/8"            |
| Ceiling Thickness | 1-1/4"            |
| Plaster Frame     | 9-1/16" x 15-1/2" |
| Pryouts           | 1/2" and 3/4"     |

P8064-EBG4



### 1100 LUMEN OPEN MODULE TRIMS FOR P8064

|  |   |  |
|--|---|--|
| <b>P8067-21A/30KG4</b><br>P8067-21A/35KG4<br>P8067-21A/40KG4<br>Clear Alzak® | <b>P8067-22A/30KG4</b><br>P8067-22A/35KG4<br>P8067-22A/40KG4<br>Gold Alzak® | <b>P8067-28/30KG4</b><br>P8067-28/35KG4<br>P8067-28/40KG4<br>White |
|--|---|--|



### 2000 LUMEN OPEN MODULE TRIMS FOR P8064

|  |   |  |
|--|---|--|
| <b>P8206-21A/30KG4</b><br>P8206-21A/35KG4<br>P8206-21A/40KG4<br>Clear Alzak® | <b>P8206-22A/30KG4</b><br>P8206-22A/35KG4<br>P8206-22A/40KG4<br>Gold Alzak® | <b>P8206-28/30KG4</b><br>P8206-28/35KG4<br>P8206-28/40KG4<br>White |
|--|---|--|



PROGRESS LED

#### FEATURES

- Universal 120-277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers included
- Suitable for wet locations, non-IC rated
- 5 year warranty

RECESSED

## 6" Pro-Optic®

### 6" NEW CONSTRUCTION HOUSING

|                   |   |
|-------------------|---|
| Product No.       | <b>P8216-EB</b><br>P8216-DM<br>P8216-277EB<br>P8216-277DM |
| Ceiling Opening   | 6-1/4"  |
| Ceiling Thickness | 1-1/4"  |
| Plaster Frame     | 9-1/8" x 14"  |
| Pryouts           | 1/2" and 3/4"   |
| Note              | Built to order with a 2-4 week lead time                  |

P8216-EB  
P8216-DM  
P8216-277EB  
P8216-277DM



### 900 LUMEN OPEN MODULE TRIMS FOR P8216

|  |
|--|
| <b>P8104-28/30K</b><br>P8104-28/35K<br>P8104-28/40K<br>White |
|--|



### 1300 LUMEN OPEN MODULE TRIMS FOR P8216

|  |
|--|
| <b>P8105-28/30K</b><br>P8105-28/35K<br>P8105-28/40K<br>White |
|--|



### 1500 LUMEN OPEN MODULE TRIMS FOR P8216

|  |
|--|
| <b>P8106-28/30K</b><br>P8106-28/35K<br>P8106-28/40K<br>White |
|--|



#### FEATURES

- Universal 120-277V high efficiency driver
- 3000K, 3500K and 4000K options
- 80+ CRI
- TM-21 50,000 hour life
- J-box rated for (8) #12-90° conductors (4 in/4 out)
- Suitable for wet locations, non-IC rated
- 5 year warranty

## 2" Pro-Optic®

### 2" NEW CONSTRUCTION HOUSING & TRIM

|                   |                 |
|-------------------|-----------------|
| Product No.       | <b>P8152-EB</b> |
| Ceiling Opening   | 2-7/8"          |
| Ceiling Thickness | 1/2" - 1-1/4"   |
| Pryouts           | 1/2"            |

### ACCESSORY FOR 2"

|             |                          |
|-------------|--------------------------|
| Product No. | <b>P8556-01</b>          |
| Description | IC Box with bar hangars. |

|                                       |                               |
|---------------------------------------|-------------------------------|
| <b>P8152-21A/27K9</b><br>Clear Alzak® | <b>P8152-28/27K9</b><br>White |
|---------------------------------------|-------------------------------|



### WALL WASH

|                                       |                               |
|---------------------------------------|-------------------------------|
| <b>P8153-21A/27K9</b><br>Clear Alzak® | <b>P8153-28/27K9</b><br>White |
|---------------------------------------|-------------------------------|



#### FEATURES

- 120V high efficiency driver
- 2700K
- TM-21 50,000 hour life
- 900 lumens
- 21 watts
- 35° distribution
- 95+ CRI
- Suitable for wet locations, non-IC rated
- Forward phase dimmable to 10%
- 5 year warranty
- Completely accessible from below the ceiling








RECESSED

# 8" Pro-Optic®

## 8" NEW CONSTRUCTION HOUSING

|                   |  |
|-------------------|--|
| Product No.       | <b>P8220-EB120VG4</b><br><b>P8220-EB277VG4</b> |
| Ceiling Opening   | 6-1/4"   |
| Ceiling Thickness | 1-1/4"   |
| Plaster Frame     | 9-1/16" x 15-1/2"                              |
| Pryouts           | 1/2" and 3/4"                                  |


P8220-EB120VG4  
P8220-EB277VG4



## 8" NEW CONSTRUCTION HOUSING

|                   |                   |
|-------------------|-------------------|
| Product No.       | <b>P8103-EBG4</b> |
| Ceiling Opening   | 6-1/4"            |
| Ceiling Thickness | 1-1/4"            |
| Plaster Frame     | 9-1/16" x 15-1/2" |
| Pryouts           | 1/2" and 3/4"     |

P8103-EBG4



## 3000 LUMEN OPEN MODULE TRIMS FOR P8220

|  |   |  |
|--|---|--|
| <b>P8120-21A/30KG4</b><br><b>P8120-21A/35KG4</b><br><b>P8120-21A/40KG4</b><br>Clear Alzak® | <b>P8120-22A/30KG4</b><br><b>P8120-22A/35KG4</b><br><b>P8120-22A/40KG4</b><br>Gold Alzak® | <b>P8120-28/30KG4</b><br><b>P8120-28/35KG4</b><br><b>P8120-28/40KG4</b><br>White |
|--|---|--|



## 1100 LUMEN OPEN MODULE TRIMS FOR P8103

|  |   |  |
|--|---|--|
| <b>P8121-21A/30KG4</b><br><b>P8121-21A/35KG4</b><br><b>P8121-21A/40KG4</b><br>Clear Alzak® | <b>P8121-22A/30KG4</b><br><b>P8121-22A/35KG4</b><br><b>P8121-22A/40KG4</b><br>Gold Alzak® | <b>P8121-28/30KG4</b><br><b>P8121-28/35KG4</b><br><b>P8121-28/40KG4</b><br>White |
|--|---|--|



## 2000 LUMEN OPEN MODULE TRIMS FOR P8103

|  |   |  |
|--|---|--|
| <b>P8133-21A/30KG4</b><br><b>P8133-21A/35KG4</b><br><b>P8133-21A/40KG4</b><br>Clear Alzak® | <b>P8133-22A/30KG4</b><br><b>P8133-22A/35KG4</b><br><b>P8133-22A/40KG4</b><br>Gold Alzak® | <b>P8133-28/30KG4</b><br><b>P8133-28/35KG4</b><br><b>P8133-28/40KG4</b><br>White |
|--|---|--|



PROGRESS LED

### FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers incl.
- Suitable for wet locations, non-IC rated
- 5 year warranty

### FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers incl.
- Suitable for wet locations, non-IC rated
- 5 year warranty

RECESSED

# 8" Pro-Optic®

## 8" RETROFIT HOUSING

|                                 |                           |
|---------------------------------|---------------------------|
| Product No.                     | <b>P8102-EBG4</b>         |
| Ceiling Opening                 | min. 8-1/8" max. 8-3/4"   |
| Product No. (Must use WF trims) | <b>P8102-EBSDG4</b>       |
| Ceiling Opening                 | min. 7-15/16" max. 8-1/8" |
| Ceiling Thickness               | 1-1/2"                    |
| Plaster Frame                   | 9" x 13-3/4" to 16"       |
| Pryouts                         | 1/2" and 3/4"             |

P8102-EBG4  
P8102-EBSDG4



## 8" RETROFIT HOUSING

|                                 |  |
|---------------------------------|--|
| Product No.                     | <b>P8215-EB120VG4</b><br><b>P8215-EB277VG4</b>     |
| Ceiling Opening                 | min. 8-1/8" max. 8-3/4"                            |
| Product No. (Must use WF trims) | <b>P8215-EBSD120VG4</b><br><b>P8215-EBSD277VG4</b> |
| Ceiling Opening                 | min. 7-15/16" max. 8-1/8"                          |
| Ceiling Thickness               | 1-1/2"   |
| Plaster Frame                   | 9" x 13-3/4" to 16"                                |
| Pryouts                         | 1/2" and 3/4"                                      |

P8215-EB120VG4  
P8215-EB277VG4  
P8215-EBSD120VG4  
P8215-EBSD277VG4



progresslighting.com

## 1100 LUMEN OPEN MODULE TRIMS FOR P8102-EB

|  |   |  |
|--|---|--|
| <b>P8121-21A/30KG4</b><br><b>P8121-21A/35KG4</b><br><b>P8121-21A/40KG4</b><br>Clear Alzak® | <b>P8121-22A/30KG4</b><br><b>P8121-22A/35KG4</b><br><b>P8121-22A/40KG4</b><br>Gold Alzak® | <b>P8121-28/30KG4</b><br><b>P8121-28/35KG4</b><br><b>P8121-28/40KG4</b><br>White |
|--|---|--|



## 1100 LUMEN OPEN MODULE TRIMS FOR P8102-EBSD

|  |   |  |
|--|---|--|
| <b>P8121-21A/30KWF64</b><br><b>P8121-21A/35KWF64</b><br><b>P8121-21A/40KWF64</b><br>Clear Alzak® | <b>P8121-22A/30KWF64</b><br><b>P8121-22A/35KWF64</b><br><b>P8121-22A/40KWF64</b><br>Gold Alzak® | <b>P8121-28/30KWF64</b><br><b>P8121-28/35KWF64</b><br><b>P8121-28/40KWF64</b><br>White |
|--|---|--|



## 2000 LUMEN OPEN MODULE TRIMS FOR P8102-EB

|  |   |  |
|--|---|--|
| <b>P8133-21A/30KG4</b><br><b>P8133-21A/35KG4</b><br><b>P8133-21A/40KG4</b><br>Clear Alzak® | <b>P8133-22A/30KG4</b><br><b>P8133-22A/35KG4</b><br><b>P8133-22A/40KG4</b><br>Gold Alzak® | <b>P8133-28/30KG4</b><br><b>P8133-28/35KG4</b><br><b>P8133-28/40KG4</b><br>White |
|--|---|--|



## 2000 LUMEN OPEN MODULE TRIMS FOR P8102-EBSD

|  |   |  |
|--|---|--|
| <b>P8133-21A/30KWF64</b><br><b>P8133-21A/35KWF64</b><br><b>P8133-21A/40KWF64</b><br>Clear Alzak® | <b>P8133-22A/30KWF64</b><br><b>P8133-22A/35KWF64</b><br><b>P8133-22A/40KWF64</b><br>Gold Alzak® | <b>P8133-28/30KWF64</b><br><b>P8133-28/35KWF64</b><br><b>P8133-28/40KWF64</b><br>White |
|--|---|--|



PROGRESS LED

### FEATURES

- Universal 120-277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Suitable for wet locations, non-IC rated
- 5 year warranty

### FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Suitable for wet locations, non-IC rated
- 5 year warranty



RECESSED

# 6" Pro-Optic® Firebox®



# Exit & Emergency

## 6" LED FIRE RATED HOUSING


|                 |                   |
|-----------------|-------------------|
| Product No.     | <b>P821-FBLED</b> |
| Ceiling Opening | 6-7/8"            |
| Recessed Depth  | 8-9/16"           |
| Plaster Frame   | 12-3/8"- 9-9/16"  |
| Pryouts         | 1/2" and 3/4"     |

P821-FBLED



## P8071 LED TRIMS (see page 58 for details)

**P8071-28/30K9-AC1-L07**  
**P8071-20/30K9-AC1-L07**  
**P8071-31/30K9-AC1-L07**  
**P8071-82/30K9-AC1-L07**  
700 lumen



**P8071-28/30K9-L10-STR2**  
**P8071-28/35K9-L10-STR2**  
1000 lumen



### FEATURES

- IC rated
- Fits into 2" x 10" construction
- CUL and UL listed for wet location when used w/P8071 (sold separately)
- UL classified to maintain fire ratings of 2 hour or less (see spec sheet for ceiling/floor designs)



## Recessed Accessories

### BAR HANGARS

|             |  |
|-------------|--|
| Product No. | <b>P8716-01</b>  |
| Description | Two 26" adjustable hangers for step lights, complete rounds and squares. |

P8716-01



|             |  |
|-------------|--|
| Product No. | <b>P8725-01</b>  |
| Description | Bar Hangar for T-Bar. For use with P8200/8201/P82002/P8203 |

|             |  |
|-------------|--|
| Product No. | <b>P8739-01</b>  |
| Description | Bar Hangar for joist. For use with P8200/8201/P82002/P8203 |

## ENERGY SAVING EMERGENCY LED EXIT SIGNS

|             |  |
|-------------|--|
| Product No. | <b>PE008-30</b> White with Red Letters<br><b>PE009-30</b> White with Green Letters |
| Description | Emergency Exit Sign  |
| Size        | 11-1/2" W., 7-1/8" ht. Extends 2".   |

PE008-30



PE009-30



|             |  |
|-------------|--|
| Product No. | <b>PE010-30</b> White with Red Letters<br><b>PE011-30</b> White with Green Letters |
| Description | Combination Exit/Emergency Light   |
| Size        | 18" W., 7-1/8" ht. Extends 4-1/3".   |

PE010-30



PE011-30



|             |                               |
|-------------|-------------------------------|
| Product No. | <b>PE012-30</b> White         |
| Description | Dual LED head emergency light |
| Size        | 9" W., 4" ht. Extends 2-3/4". |

PE012-30



### FEATURES

- Dual LED head emergency light
- LED life-cycle of more than 10 years
- Quick installation, dual-voltage 120 or 277V AC input
- 3 VDC, 1 W Lamp
- Includes long-life Nickel Cadmium battery for UL recognized 90 minutes emergency lighting
- Damp location listed
- Fully adjustable lamp-heads
- Provided with test switch and AC-on indicator.

### FEATURES

- Universal face
- LED life-cycle of more than 10 years
- Molded-in template for quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minutes emergency lighting
- Damp location listed
- Provided with test switch and AC-on indicator
- Canopy included
- 2 year full unit warranty

### FEATURES

- Combination Exit/Emergency Light
- Universal face
- LED life-cycle of more than 10 years
- Molded-in template for quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minutes emergency lighting
- Damp location listed
- Provided with test switch and AC-on indicator
- Canopy included
- Lamp-heads are fully adjustable

### 17 - WATT

Dimmable to 10% brightness with ELV type dimmers.  
See list below for known compatible controls:

**LUTRON\*\*\***

- DVELV-300P
- NTELV-300
- VTELV-600
- MAELV-600
- SPSELV-600

**LEVITON:**

- AWRMG-EAW

### 9 / 10.5 / 12 - WATT

Dimmable to 10% brightness with ELV type dimmers.  
See list below for known compatible controls:

**LUTRON\*\*\***

- DVELV-300P
- NTELV-300
- VTELV-600
- AYCL-153P
- DVCL-153P
- MAELV-600
- SPSELV-600

**LEVITON:**

- AWRMG-EAW

### REPLACEMENT PART FOR INTERGRAL LED LIGHT ENGINE

|     |                 |
|-----|-----------------|
| 17w | <b>93053641</b> |
| 9w  | <b>93054049</b> |

\* We do not recommend using digital dimmer controls  
 \*\* Compatibility with incandescent dimmers varies by load, due to this factor, we recommend ELV type dimmers for best performance.  
 \*\*\* Applicable trademark, copyright and other intellectual property laws protect all of our brand features. If you would like to use any of our brand features on your website, in an ad, in any other medium, you may need to receive permission from Progress Lighting first.

### PRO-OPTIC 0-10V DIMMING

Pro-Optic LED driver is compatible with 0-10V type dimming controls. Recommended dimming controls are listed below.

| CONTROL MANUFACTURER           | WALLBOX DIMMER  | POWER BOOSTER AVAILABLE |
|--------------------------------|---|-------------------------|
| Douglas Lighting controls      | WPC 5721  |                         |
| Entertainment Technology       | Tap Glide TG600FAM120 (120V)<br>Tap Glide Heatsink TGH1500FAM120 (120V)<br>Oasis OA2000FAMU (120/277V)  |                         |
| Honeywell, Inc.                | EL 7315A1019 and EL7315A1009  | EL7305A1010             |
| HUNT Dimming                   | Preset Slide: PS-010-IV-120V and PS-010-WH-120V<br>Preset Slide: PS-010-3W-IV-120V and PS-010-3W-WH-120V<br>Preset Slide: PS-010-IV-277V and PS-010-WH-277V<br>Preset Slide: PS-010-3W-IV-277V and PS-010-3W-WH-277V<br>Preset Slide, controls FD-010: PS-IFC-010-IV- and PS-IFC-010-WH-120/277V<br>Preset Slide, controls FD-010: PS-IFC-010-3W-IV- and PS-IFC-010-3W-WH-120/277V<br>Remoted mounted unit: FD-010-120V and FD-010-277V |                         |
| Lehigh Electric Products Co.   | Solitaire PBX   |                         |
| Leviton Lighting Controls Div. | Leviton Centura Fluorescent Control System<br>IllumaTech™ IP7 Series  | CN100<br>PE300          |
| Lightolier Controls            | Sunrise Preset slider ZP600FAM120 (120V)<br>Momentum Preset slider MP1500FAM120 (120V)<br>Vega Slider V2000FAMU (120/277)   |                         |
| Lithonia Controls              | ISD BC<br>SLD LPCS<br>Digital Equinox (DEQ BC)  | RDM FC                  |
| Lutron Electronics Co., Inc.   | Visit <a href="http://www.lutron.com/advance">www.lutron.com/advance</a> for the latest control information and selection   |                         |
| PDM Electrical products        | WPC-5721  |                         |
| Starfield Controls             | TR61 with DALI interface port   | RT03 DAL Inet router    |
| The Watt Stopper, Inc.         | LS4 used with LCD-101 and LCD-103   |                         |

For the current list of dimming options please see [progresslighting.com/dimmers](http://progresslighting.com/dimmers) or the current specification sheets on the web site.

### CLOSE-TO-CEILING

- P2300 ..... 5
- P2301 ..... 5
- P2302 ..... 4
- P2303 ..... 4
- P2304 ..... 5
- P2305 ..... 5
- P2306 ..... 10
- P2307 ..... 10
- P2308 ..... 10
- P2309 ..... 10
- P2310 ..... 10
- P2311 ..... 10
- P2321 ..... 4
- P2322 ..... 4
- P3408 ..... 12
- P3411 ..... 7
- P3417 ..... 7
- P3432 ..... 7
- P3447 ..... 6
- P3448 ..... 6
- P3449 ..... 6
- P3610 ..... 11
- P3611 ..... 11
- P3612 ..... 11
- P3658 ..... 13
- P3659 ..... 13
- P3675 ..... 12
- P3695 ..... 9
- P3737 ..... 8
- P3747 ..... 8
- P3756 ..... 9
- P3910 ..... 12
- P3911 ..... 12
- P7385 ..... 12
- P8022 ..... 2
- P8027 ..... 2
- P8222 ..... 2
- P8240 ..... 3
- P8241 ..... 3
- P8247 ..... 3

### PENDANTS

- P5023 ..... 17
- P5024 ..... 17
- P5050 ..... 16
- P5053 ..... 18
- P5075 ..... 15
- P5087 ..... 18
- P5094 ..... 18
- P5143 ..... 15
- P5186 ..... 17
- P5187 ..... 17
- P5188 ..... 16
- P5197 ..... 16

### BATH & VANITY

- P2061 ..... 22
- P2062 ..... 22
- P2063 ..... 22
- P2064 ..... 22
- P2091 ..... 19
- P2092 ..... 19
- P2093 ..... 19
- P2094 ..... 19
- P2142 ..... 20
- P2143 ..... 20
- P2144 ..... 21
- P2145 ..... 21
- P8932 ..... 23
- P8934 ..... 23

### UNDERCABINET

- P7002 ..... 26
- P7005 ..... 26
- P7012 ..... 26
- P7013 ..... 26
- P7040 ..... 24
- P7041 ..... 24
- P7042 ..... 24
- P7510 ..... 27
- P8683 ..... 24
- P8705 ..... 25
- P8711 ..... 25
- P8731 ..... 25
- P8732 ..... 25
- P8733 ..... 27
- P8735 ..... 27

### UNDERCABINET

(cont'd)

- P8737 ..... 27
- P8738 ..... 27
- P8740 ..... 27
- P8743 ..... 27
- P8744 ..... 25
- P8747 ..... 25
- P8749 ..... 25
- P8750 ..... 25
- P8752 ..... 25
- P8754 ..... 25

### SCONCES

- P2061 ..... 29
- P2091 ..... 29
- P2092 ..... 29
- P2306 ..... 28
- P2307 ..... 28
- P2308 ..... 28
- P2309 ..... 28
- P2310 ..... 28
- P2311 ..... 28
- P7083 ..... 30
- P7085 ..... 30
- P7088 ..... 30
- P7092 ..... 30
- P7093 ..... 30
- P8932 ..... 29
- P8934 ..... 29

### OUTDOOR

- P3647 ..... 50
- P3648 ..... 50
- P3649 ..... 51
- P3650 ..... 51
- P3715 ..... 51
- P3883 ..... 45
- P5390 ..... 49
- P5391 ..... 49
- P5392 ..... 49
- P5394 ..... 49
- P5445 ..... 45
- P5530 ..... 45
- P5641 ..... 46
- P5642 ..... 46
- P5674 ..... 47
- P5675 ..... 47
- P5723 ..... 42
- P5741 ..... 46
- P5749 ..... 43
- P5750 ..... 43
- P5751 ..... 43
- P5774 ..... 47
- P5862 ..... 44
- P5863 ..... 44
- P5864 ..... 44
- P6017 ..... 43
- P6056 ..... 35
- P6057 ..... 35
- P6058 ..... 35
- P6067 ..... 38
- P6068 ..... 38
- P6069 ..... 38
- P6077 ..... 36
- P6078 ..... 36
- P6079 ..... 36
- P6084 ..... 40
- P6085 ..... 40
- P6424 ..... 41
- P6427 ..... 39
- P6430 ..... 37
- P6524 ..... 41
- P6526 ..... 35
- P6527 ..... 39
- P6530 ..... 37

### OUTDOOR

(cont'd)

- P6827 ..... 52
- P6828 ..... 52
- P6829 ..... 53
- P6832 ..... 53
- P8710 ..... 48
- P8712 ..... 48
- P8726 ..... 49
- P8741 ..... 48
- P8748 ..... 49
- P8774 ..... 35
- P8775 ..... 35
- P8779 ..... 35
- P8798 ..... 48
- P8799 ..... 48
- PHSL-13-23B ..... 50

### LANDSCAPE

- P5245 ..... 54
- P5246 ..... 55
- P5247 ..... 54
- P5295 ..... 55
- P5296 ..... 55
- P5297 ..... 54
- P5298 ..... 54
- P5299 ..... 55
- P8270 ..... 55
- P8617 ..... 55
- P8626 ..... 55

### RECESSED

- P8002 ..... 63
- P8005 ..... 62
- P8006 ..... 62
- P8021 ..... 62
- P8021 ..... 63
- P8022 ..... 56
- P8023 ..... 62
- P8027 ..... 56
- P8050 ..... 62
- P8050 ..... 63
- P8051 ..... 62
- P8061 ..... 59
- P8064 ..... 60

### RECESSED

(cont'd)

- P8067 ..... 60
- P8071 ..... 58, 66
- P8080 ..... 59
- P8102 ..... 65
- P8103 ..... 64
- P8104 ..... 61
- P8105 ..... 61
- P8106 ..... 61
- P8112 ..... 62
- P8112 ..... 63
- P8120 ..... 64, 65
- P8121 ..... 64, 65
- P8123 ..... 62
- P8133 ..... 64, 65
- P8152 ..... 60
- P8153 ..... 60
- P8206 ..... 60
- P821 ..... 66
- P8212 ..... 62
- P8214 ..... 63
- P8215 ..... 65
- P8216 ..... 61
- P8220 ..... 64
- P8223 ..... 62
- P8240 ..... 57
- P8241 ..... 57
- P8247 ..... 57
- P830-LED ..... 59
- P831-LED ..... 59
- P832-LED ..... 59
- P8556 ..... 60
- P8595 ..... 57
- P8596 ..... 57
- P87-LED ..... 58
- P8716 ..... 66
- P8725 ..... 66
- P8739 ..... 66

### EXIT & EMERGENCY

- PE008 ..... 57
- PE010 ..... 57
- PE012 ..... 57