

***THE GREATEST SINGLE
SOURCE FOR CLAMPS,
STRAPS AND HANGERS***



VICTOR SPECIALTIES

1350 GARRISON AVENUE
TEL (718) 893-2763

BRONX, NEW YORK 10474
FAX: 800-221-3932

email: sales@victorsp.com

VISIT OUR WEBSITE AT www.victorspecialties.com




INDEX

| CATEGORY | PAGE NO. | CATEGORY | PAGE NO. |
|----------------------------|--------------|----------------------|--------------|
| CLAMPS | 3-11 | STRAPS | 12-20 |
| ALUMINUM | 9 | ALUMINUM | 19 |
| BRASS | 10 | BRASS | 19 |
| BX | 4 | COPPER | 19 |
| COPPER PLATED | 10 | EMT | 13 |
| DUPLEX | 8 | HEAVY WALL (RIGID) | 12 |
| EMT | 4,8,9 | PAD TYPE | 20 |
| HEAVY WALL (RIGID) | 3,9 | SERVICE ENTRANCE | 17,18 |
| SERVICE ENTRANCE | 6 | STAND OFF | 18 |
| TUBING, CABLE | 5 | TUBING, CABLE | 13-20 |
| HANGERS | 22 | MISCELLANEOUS | |
| | | PERFORATED STRAPPING | 21 |
| | | TUBING SUPPORTS | 21 |
| GANG BOXES | 23 | | |
| GANG BOX COLLARS | 24 | | |
| DEVICE COVERS | 25,26 | | |
| GANG BOX PARTITIONS | 26 | | |

HOW TO ORDER THE CORRECT SIZE VICTOR CLAMPS AND STRAPS

THERE IS A CONSIDERABLE DIFFERENCE BETWEEN THE OUTSIDE DIAMETERS OF THIN WALL CONDUIT, HEAVY WALL CONDUIT AND FRACTIONAL SIZES OF TUBING OF A GIVEN SIZE.



| FRACTIONAL INCH SIZE | ACTUAL OUTSIDE DIAMETER | THINWALL SIZE (E.M.T.) | ACTUAL OUTSIDE DIAMETER | HEAVYWALL SIZE & PIPE (RIGID) | ACTUAL OUTSIDE DIAMETER |
|----------------------------|-------------------------------|------------------------------|-------------------------------|-------------------------------------|-------------------------------|
| 1/8" | = .125" | | | 1/8 | = .405" |
| 1/4" | = .250" | | | 1/4 | = .540" |
| 3/8" | = .375" | | | 3/8 | = .675" |
| 1/2" | = .500" | 1/2 | = .706" | 1/2 | = .840" |
| 3/4" | = .750" | 3/4 | = .922" | 3/4 | = 1.050" |
| 1" | = 1.000" | 1 | = 1.163" | 1 | = 1.315" |
| 1 1/4" | = 1.250" | 1 1/4 | = 1.503" | 1 1/4 | = 1.660" |
| 1 1/2" | = 1.500" | 1 1/2 | = 1.738" | 1 1/2 | = 1.900" |
| 2" | = 2.000" | 2 | = 2.195" | 2 | = 2.375" |
| 2 1/2" | = 2.500" | 2 1/2 | = 2.875" | 2 1/2 | = 2.875" |
| 3" | = 3.000" | 3 | = 3.500" | 3 | = 3.500" |
| 3 1/2" | = 3.500" | 3 1/2 | = 4.000" | 3 1/2 | = 4.000" |
| 4" | = 4.000" | 4 | = 4.500" | 4 | = 4.500" |
| 4 1/2" | = 4.500" | | | | |
| 5" | = 5.000" | | | 5 | = 5.563" |
| 6" | = 6.000" | | | 6 | = 6.625" |




VICTOR "SNAP ON" STEEL CLAMPS

FOR HEAVY WALL CONDUIT (RIGID)

| CONDUIT SIZE (RIGID) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | |
|-------|---------|---|------|------|------|-----|------|----|
| 1/8 | 10010-S | 1 | 9/32 | .062 | 9/16 | 100 | 1000 | 15 |
| 1/4 | 10011-S | 1 | 9/32 | .062 | 9/16 | 100 | 1000 | 19 |
| 3/8 | 10012-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 1/2 | 10013-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 3/4 | 10014-S | 1 | 9/32 | .062 | 3/4 | 100 | 500 | 22 |
| 1 | 10015-S | 1 | 9/32 | .093 | 3/4 | 50 | 500 | 41 |
| 1 1/4 | 10016-S | 1 | 9/32 | .093 | 3/4 | 50 | 250 | 25 |



HEAVY SERIES

| | | | | | | | | |
|-------|---------|---|-------|------|-------|-----|------|----|
| 3/8 | 10712-S | 2 | 9/32 | .093 | 3/4 | 100 | 1000 | 43 |
| 1/2 | 10713-S | 2 | 9/32 | .093 | 3/4 | 100 | 500 | 24 |
| 3/4 | 10714-S | 2 | 9/32 | .093 | 3/4 | 100 | 500 | 31 |
| 1 | 10715-S | 2 | 13/32 | .125 | 1 | 50 | 250 | 31 |
| 1 1/4 | 10716-S | 2 | 13/32 | .125 | 1 | 25 | 125 | 21 |
| 1 1/2 | 10717-S | 2 | 13/32 | .125 | 1 | 25 | 125 | 23 |
| 2 | 10718-S | 2 | 21/32 | .125 | 1 1/2 | - | 50 | 18 |

EXTRA HEAVY SERIES

| | | | | | | | | |
|-------|---------|---|-------|------|-------|----|-----|----|
| 1/2 | 17113-S | 4 | 11/32 | .125 | 1 | 50 | 500 | 46 |
| 3/4 | 17114-S | 4 | 11/32 | .125 | 1 | 50 | 250 | 29 |
| 1 | 17115-S | 4 | 13/32 | .188 | 1 | - | 100 | 20 |
| 1 1/4 | 17116-S | 4 | 13/32 | .188 | 1 | - | 50 | 14 |
| 1 1/2 | 17117-S | 4 | 13/32 | .250 | 1 | - | 50 | 20 |
| 2 | 17118-S | 4 | 21/32 | .250 | 1 1/2 | - | 25 | 19 |
| 2 1/2 | 17119-S | 4 | 21/32 | .250 | 1 1/2 | - | 25 | 25 |
| 3 | 17120-S | 4 | 21/32 | .250 | 1 1/2 | - | 25 | 30 |
| 3 1/2 | 17121-S | 4 | 21/32 | .250 | 1 1/2 | - | 20 | 25 |
| 4 | 17122-S | 4 | 21/32 | .250 | 1 1/2 | - | 20 | 28 |
| 5 | 17124-S | 4 | 21/32 | .375 | 1 1/2 | - | 10 | 24 |
| 6 | 17125-S | 4 | 21/32 | .375 | 1 1/2 | - | 5 | 15 |



SMALL HOLE CLAMPS

| | | | | | | | | |
|-----|---------|---|-------|------|-------|-----|------|----|
| 1/8 | 19110-S | 4 | 7/32 | .062 | 9/16 | 100 | 1000 | 15 |
| 1/4 | 19111-S | 4 | 7/32 | .062 | 9/16 | 100 | 1000 | 19 |
| 3/8 | 19112-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 1/2 | 19113-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 3/4 | 19114-S | 4 | 7/32 | .062 | 3/4 | 100 | 500 | 22 |
| 2 | 19118-S | 4 | 13/32 | .125 | 1 1/2 | - | 50 | 17 |



SLOTTED HOLE CLAMPS

| | | | | | | | | |
|-----|---------|---|------------|------|-----|-----|------|----|
| 3/8 | 18712-S | 4 | 9/32 X 1/2 | .093 | 3/4 | 100 | 1000 | 47 |
| 1/2 | 18713-S | 4 | 9/32 X 1/2 | .093 | 3/4 | 100 | 500 | 27 |
| 3/4 | 18714-S | 4 | 9/32 X 1/2 | .093 | 3/4 | 100 | 500 | 33 |
| 1 | 18715-S | 4 | 9/32 X 1/2 | .125 | 1 | 50 | 250 | 37 |





BLANK CLAMPS - STANDARD SERIES (TAIL LENGTH 1 1/8")

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|-----|----|
| 1/2 | 15013-S | 4 | NONE | .062 | 3/4 | 100 | 500 | 21 |
| 3/4 | 15014-S | 4 | NONE | .062 | 3/4 | 100 | 500 | 24 |

BLANK CLAMPS - HEAVY SERIES (TAIL LENGTH 1 1/8")

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|-----|----|
| 1/2 | 15713-S | 4 | NONE | .093 | 3/4 | 100 | 500 | 33 |
| 3/4 | 15714-S | 4 | NONE | .093 | 3/4 | 100 | 500 | 37 |






VICTOR "SNAP ON" STEEL CLAMPS

FOR THIN WALL CONDUIT (E.M.T.)

| CONDUIT SIZE (E.M.T.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|-----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|-----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | |
|-------|---------|---|------|------|-----|-----|------|----|
| 1/2 | 10043-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 24 |
| 3/4 | 10044-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 1 | 10045-S | 1 | 9/32 | .062 | 3/4 | 100 | 500 | 22 |
| 1 1/4 | 10046-S | 1 | 9/32 | .093 | 3/4 | 50 | 250 | 23 |



HEAVY SERIES

| | | | | | | | | |
|-------|---------|---|-------|------|-------|-----|------|----|
| 1/2 | 10743-S | 2 | 9/32 | .093 | 3/4 | 100 | 1000 | 43 |
| 3/4 | 10744-S | 2 | 9/32 | .093 | 3/4 | 100 | 500 | 28 |
| 1 | 10745-S | 2 | 9/32 | .093 | 3/4 | 50 | 500 | 36 |
| 1 1/4 | 10746-S | 2 | 13/32 | .125 | 1 | 25 | 125 | 20 |
| 1 1/2 | 10747-S | 2 | 13/32 | .125 | 1 | 25 | 125 | 22 |
| 2 | 10748-S | 2 | 21/32 | .125 | 1 1/2 | - | 50 | 17 |

EXTRA HEAVY SERIES

| | | | | | | | | |
|-------|---------|---|-------|------|-------|---|----|----|
| 1 1/4 | 17146-S | 4 | 13/32 | .188 | 1 | - | 50 | 13 |
| 1 1/2 | 17147-S | 4 | 13/32 | .250 | 1 | - | 50 | 18 |
| 2 | 17148-S | 4 | 21/32 | .250 | 1 1/2 | - | 25 | 17 |
| 2 1/2 | 17119-S | 4 | 21/32 | .250 | 1 1/2 | - | 25 | 25 |
| 3 | 17120-S | 4 | 21/32 | .250 | 1 1/2 | - | 25 | 30 |
| 3 1/2 | 17121-S | 4 | 21/32 | .250 | 1 1/2 | - | 20 | 25 |
| 4 | 17122-S | 4 | 21/32 | .250 | 1 1/2 | - | 20 | 28 |



SMALL HOLE CLAMPS

| | | | | | | | | |
|-----|---------|---|-------|------|-------|-----|------|----|
| 1/2 | 19143-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 3/4 | 19144-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 1 | 19145-S | 4 | 7/32 | .062 | 3/4 | 100 | 500 | 22 |
| 2 | 19148-S | 4 | 13/32 | .125 | 1 1/2 | - | 50 | 17 |




SLOTTED HOLE CLAMPS

| | | | | | | | | |
|-----|---------|---|----------|------|-----|-----|------|----|
| 1/2 | 18743-S | 4 | 9/32X1/2 | .093 | 3/4 | 100 | 1000 | 37 |
| 3/4 | 18744-S | 4 | 9/32X1/2 | .093 | 3/4 | 100 | 500 | 30 |
| 1 | 18745-S | 4 | 9/32X1/2 | .093 | 3/4 | 50 | 500 | 38 |



BLANK CLAMPS - STANDARD SERIES (TAIL LENGTH 1 1/8")

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|------|----|
| 1/2 | 15043-S | 4 | NONE | .062 | 3/4 | 100 | 1000 | 37 |
| 3/4 | 15044-S | 4 | NONE | .062 | 3/4 | 100 | 500 | 23 |



BLANK CLAMPS - HEAVY SERIES (TAIL LENGTH 1 1/8")

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|-----|----|
| 1/2 | 15743-S | 4 | NONE | .093 | 3/4 | 100 | 500 | 31 |
| 3/4 | 15744-S | 4 | NONE | .093 | 3/4 | 100 | 500 | 35 |



VICTOR "SNAP ON" STEEL CLAMPS

FOR "BX" CABLE

| "BX" CABLE | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|------------------------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
| 14-3 TO 12-3 | 11105-S | 2 | 9/32 | .062 | 9/16 | 100 | 1000 | 17 |
| & 3/8 FLEX | 19105-S | 4 | 7/32 | .062 | 9/16 | 100 | 1000 | 18 |
| 12-4 TO 10-4 & 3/8 SHELL GROUND | 11106-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 20 |



BX cable outer diameters may vary by manufacturer and material.

VICTOR STEEL CLAMPS

FOR TUBING AND CABLE

| TUBING DIA. (O.D.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES


| | | | | | | | | |
|------|---------|---|-------|------|-----|-----|------|---|
| 3/32 | 10543-S | 1 | 5/32 | .032 | 3/8 | 100 | 1000 | 3 |
| 1/8 | 10545-S | 1 | 5/32 | .032 | 3/8 | 100 | 1000 | 3 |
| 5/32 | 10547-S | 1 | 5/32 | .032 | 3/8 | 100 | 1000 | 3 |
| 3/16 | 10550-S | 1 | 5/32 | .032 | 3/8 | 100 | 1000 | 4 |
| 1/4 | 10551-S | 1 | 5/32 | .032 | 3/8 | 100 | 1000 | 4 |
| 5/16 | 10552-S | 1 | 5/32 | .032 | 3/8 | 100 | 1000 | 5 |
| 3/8 | 10553-S | 1 | 5/32 | .032 | 3/8 | 100 | 1000 | 5 |
| 3/32 | 10563-S | 1 | 13/64 | .032 | 3/8 | 100 | 1000 | 3 |
| 1/8 | 10565-S | 1 | 13/64 | .032 | 3/8 | 100 | 1000 | 3 |
| 5/32 | 10567-S | 1 | 13/64 | .032 | 3/8 | 100 | 1000 | 3 |
| 3/16 | 10570-S | 1 | 13/64 | .032 | 3/8 | 100 | 1000 | 4 |
| 1/4 | 10571-S | 1 | 13/64 | .032 | 3/8 | 100 | 1000 | 4 |
| 5/16 | 10572-S | 1 | 13/64 | .032 | 3/8 | 100 | 1000 | 5 |
| 3/8 | 10573-S | 1 | 13/64 | .032 | 3/8 | 100 | 1000 | 5 |



HEAVY SERIES

| | | | | | | | | |
|------|---------|---|-------|------|-----|-----|------|----|
| 1/8 | 10585-S | 1 | 13/64 | .062 | 3/8 | 100 | 1000 | 6 |
| 5/32 | 10587-S | 1 | 13/64 | .062 | 3/8 | 100 | 1000 | 6 |
| 3/16 | 10590-S | 1 | 13/64 | .062 | 3/8 | 100 | 1000 | 7 |
| 1/4 | 10591-S | 1 | 13/64 | .062 | 3/8 | 100 | 1000 | 7 |
| 5/16 | 10592-S | 1 | 13/64 | .062 | 3/8 | 100 | 1000 | 8 |
| 3/8 | 10593-S | 1 | 13/64 | .062 | 3/8 | 100 | 1000 | 8 |
| 1/4 | 11101-S | 2 | 7/32 | .062 | 1/2 | 100 | 1000 | 10 |
| 5/16 | 11102-S | 2 | 7/32 | .062 | 1/2 | 100 | 1000 | 12 |
| 3/8 | 11103-S | 2 | 7/32 | .062 | 1/2 | 100 | 1000 | 12 |

HEAVY SERIES - "V" SHAPE



| | | | | | | | | |
|-----------|---------|---|------|------|-----|-----|------|----|
| 1/8-3/16 | 11100-S | 2 | 7/32 | .062 | 1/2 | 100 | 1000 | 8 |
| 1/8-3/16 | 11150-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 10 |
| 5/16-7/16 | 10802-S | 2 | 7/32 | .062 | 1/2 | 100 | 1000 | 11 |
| 7/16-1/2 | 19104-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 18 |
| 7/16-1/2 | 10804-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 18 |

EXTRA HEAVY SERIES



| | | | | | | | | |
|-------|---------|---|------|------|------|-----|------|----|
| 1/4 | 11151-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 13 |
| 5/16 | 11152-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 15 |
| 3/8 | 11153-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 17 |
| 7/16 | 11104-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 16 |
| 1/2 | 11105-S | 2 | 9/32 | .062 | 9/16 | 100 | 1000 | 17 |
| 9/16 | 11106-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 20 |
| 5/8 | 11108-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 24 |
| 11/16 | 11110-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 3/4 | 11112-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 28 |
| 13/16 | 11115-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 7/8 | 11120-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 15/16 | 11122-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 33 |
| 1 | 11125-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 36 |
| 1 1/4 | 11130-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 20 |


VICTOR STEEL CLAMPS

FOR SERVICE ENTRANCE CABLE

| CABLE SIZE & DESCRIPTION | VICTOR PART NUMBER | PRICE LIST PAGE | A | B | D | T | W | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------------|--------------------|-----------------|---|---|---|---|---|----------------|-------------------|----------------|
|--------------------------|--------------------|-----------------|---|---|---|---|---|----------------|-------------------|----------------|


STANDARD SERIES

| | | | | | | | | | | |
|----------------|---------|---|-------|-------|------|------|-----|-----|------|----|
| 8-3 & 8-AWG-3C | 10076-S | 1 | 11/16 | 3/8 | 9/32 | .062 | 5/8 | 100 | 1000 | 21 |
| 6-3 | 10082-S | 1 | 23/32 | 1/2 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 6-2 & 8-1 | | | | | | | | | | |
| 4-3 | 10084-S | 1 | 7/8 | 17/32 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 2-3 | 10085-S | 1 | 31/32 | 17/32 | 9/32 | .062 | 5/8 | 100 | 1000 | 28 |
| 2-2 & 4-1 | | | | | | | | | | |
| 2-3 | 10086-S | 1 | 1 | 5/8 | 9/32 | .062 | 5/8 | 100 | 1000 | 32 |
| 8-3 & 8-AWG-3C | 19176-S | 4 | 11/16 | 3/8 | 7/32 | .062 | 5/8 | 100 | 1000 | 21 |
| 6-3 | 19182-S | 4 | 23/32 | 1/2 | 7/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 6-2 & 8-1 | | | | | | | | | | |
| 4-3 | 19184-S | 4 | 7/8 | 17/32 | 7/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 2-3 | 19186-S | 4 | 1 | 5/8 | 7/32 | .062 | 5/8 | 100 | 1000 | 32 |




HEAVY SERIES

| | | | | | | | | | | |
|----------------|---------|---|---------|--------|------|------|-----|-----|------|----|
| 8-3 & 8-AWG-3C | 10776-S | 2 | 11/16 | 3/8 | 9/32 | .093 | 3/4 | 100 | 1000 | 41 |
| 6-3 | 10782-S | 2 | 23/32 | 1/2 | 9/32 | .093 | 3/4 | 100 | 1000 | 47 |
| 6-2 & 8-1 | | | | | | | | | | |
| 4-3 | 10784-S | 2 | 7/8 | 17/32 | 9/32 | .093 | 3/4 | 100 | 1000 | 49 |
| 2-3 | 10785-S | 2 | 31/32 | 17/32 | 9/32 | .093 | 3/4 | 100 | 500 | 25 |
| 2-2 & 4-1 | | | | | | | | | | |
| 2-3 | 10786-S | 2 | 1 | 5/8 | 9/32 | .093 | 3/4 | 100 | 500 | 28 |
| 2-3(OLD) | 10790-S | 2 | 1 1/16 | 5/8 | 9/32 | .093 | 3/4 | 100 | 500 | 30 |
| 1-3 | 10793-S | 2 | 1 3/16 | 5/8 | 9/32 | .093 | 3/4 | 100 | 500 | 30 |
| 2/0-3 | 10795-S | 2 | 1 9/32 | 21/32 | 9/32 | .093 | 3/4 | 100 | 500 | 31 |
| 2/0-2 & 1-1 | | | | | | | | | | |
| 2/0-3 | 10796-S | 2 | 1 7/16 | 3/4 | 9/32 | .120 | 1 | 50 | 250 | 31 |
| 4/0-2 & 2/0-1 | 10797-S | 2 | 1 15/32 | 7/8 | 9/32 | .120 | 1 | 50 | 250 | 34 |
| 4/0-3 | 10798-S | 2 | 1 11/16 | 15/16 | 9/32 | .120 | 1 | 50 | 250 | 36 |
| 4/0-3 | 10799-S | 2 | 1 3/4 | 1 1/16 | 9/32 | .120 | 1 | 50 | 250 | 38 |



LIGHT WEIGHT FOR ROMEX CABLE

| | | | | | | | | | | |
|------------|---------|---|-------|-------|-------|------|-----|-----|------|----|
| 12-2, 14-2 | 10090-S | 1 | 19/32 | 11/32 | 13/64 | .032 | 1/2 | 100 | 1000 | 10 |
|------------|---------|---|-------|-------|-------|------|-----|-----|------|----|




Sample clamps are available to determine best fit.

VICTOR STEEL CLAMPS

FOR UF CABLE "ROMEX" AND "P.V.C."


| CABLE SIZE & DESCRIPTION | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|--------------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

UF CABLE



| | | | | | | | | |
|------------------------------|---------|---|------|------|-----|-----|------|----|
| 10-2 | 15323-S | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 10 |
| 10-3, 10-3 WITH GROUND 600V | 19103-S | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 10 |
| 12-2, 14-2, 16-3 S.P.T. CORD | 10072-S | 1 | 7/32 | .062 | 1/2 | 100 | 1000 | 10 |
| 12-3 | 19178-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 17 |


P.V.C. AND ROMEX CABLE



| | | | | | | | | |
|------------|---------|---|------|------|------|-----|------|----|
| 12-2, 14-2 | 10080-S | 1 | 7/32 | .062 | 9/16 | 100 | 1000 | 14 |
| 12-2, 14-2 | 10081-S | 1 | 7/32 | .062 | 9/16 | 100 | 1000 | 18 |
| 12-3, 14-3 | 19104-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 18 |

VICTOR STEEL GANG CLAMPS

MADE OF .062 X 1/2 STEEL WITH 7/32 MOUNTING HOLE



| VICTOR PART NUMBER | NUMBER OF LINES | PRICE LIST PAGE | "A" DIM. | "B" DIM. | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|-----------------|-----------------|----------|----------|----------------|-------------------|----------------|
| 15321-S | 2 | 4 | 5/32 | 1/8 | 100 | 1000 | 8 |
| 15322-S | 3 | 4 | 5/16 | 1/8 | 100 | 1000 | 9 |
| 15323-S | 4 | 4 | 15/32 | 1/8 | 100 | 1000 | 10 |
| 15324-S | 5 | 4 | 5/8 | 1/8 | 100 | 1000 | 11 |
| 15325-S | 6 | 4 | 25/32 | 1/8 | 100 | 1000 | 11 |
| 15326-S | 7 | 4 | 15/16 | 1/8 | 100 | 1000 | 12 |
| 15327-S | 8 | 4 | 1-3/32 | 1/8 | 100 | 1000 | 15 |
| 15328-S | 9 | 4 | 1-1/4 | 1/8 | 100 | 1000 | 14 |
| 19102-S | 2 | 4 | 1/2 | 7/32 | 100 | 1000 | 12 |
| 19103-S | 3 | 4 | 3/4 | 7/32 | 100 | 1000 | 10 |

VICTOR STEEL DUPLEX CLAMPS

FOR UF CABLE "ROMEX" AND "P.V.C."


| TUBE DIAMETER (O.D.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | |
|------|---------|---|------|------|-----|-----|------|---|
| 3/16 | 10690-S | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 5 |
| 1/4 | 10691-S | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 6 |
| 5/16 | 10692-S | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 7 |
| 3/8 | 10693-S | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 9 |

HEAVY SERIES

| | | | | | | | | |
|------------|---------|---|------|------|-----|-----|------|----|
| 1/4 | 12701-S | 3 | 7/32 | .062 | 1/2 | 100 | 1000 | 16 |
| 5/16 | 12702-S | 3 | 7/32 | .062 | 1/2 | 100 | 1000 | 18 |
| 3/8 | 12703-S | 3 | 7/32 | .062 | 1/2 | 100 | 1000 | 21 |
| 1/2 | 12705-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 32 |
| 5/8 | 12708-S | 3 | 9/32 | .062 | 5/8 | 100 | 500 | 17 |
| 3/4 | 12712-S | 3 | 9/32 | .062 | 5/8 | 100 | 500 | 19 |
| 7/16 | 13104-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 24 |
| 9/16 | 13106-S | 3 | 9/32 | .062 | 5/8 | 100 | 500 | 13 |
| 11/16 | 13110-S | 3 | 9/32 | .062 | 5/8 | 100 | 500 | 19 |
| 13/16 | 13115-S | 3 | 9/32 | .062 | 5/8 | 100 | 500 | 24 |
| 1/2 E.M.T. | 12743-S | 3 | 9/32 | .062 | 5/8 | 100 | 500 | 22 |



VICTOR 200 SERIES


FOR THIN WALL CONDUIT (E.M.T.)

| CONDUIT SIZE (E.M.T.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|-----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|-----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | |
|-----|-----------|-----|------|------|-------|-----|------|----|
| 1/2 | 20043-S | N/A | 9/32 | .042 | 9/16 | 100 | 1000 | 14 |
| 3/4 | 20044-S | N/A | 9/32 | .042 | 19/32 | 100 | 1000 | 19 |
| 1 | 20045-S | N/A | 9/32 | .048 | 3/4 | 100 | 500 | 17 |
| 1/2 | 20043-SB* | N/A | 9/32 | .042 | 9/16 | - | 1000 | 14 |
| 3/4 | 20044-SB* | N/A | 9/32 | .042 | 19/32 | - | 1000 | 19 |

* BULK PACKED




VICTOR STEEL SAFETY CLAMPS

FOR CABLE OR TUBING

| TUBING DIA. (O.D.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | |
|------|---------|---|------|------|-----|-----|------|----|
| 1/4 | 16101-S | 4 | 9/32 | .032 | 5/8 | 100 | 1000 | 15 |
| 5/16 | 16102-S | 4 | 9/32 | .032 | 5/8 | 100 | 1000 | 16 |
| 3/8 | 16103-S | 4 | 9/32 | .032 | 5/8 | 100 | 1000 | 17 |
| 1/2 | 16105-S | 4 | 9/32 | .032 | 5/8 | 100 | 1000 | 21 |
| 5/8 | 16108-S | 4 | 9/32 | .032 | 3/4 | 100 | 500 | 14 |
| 3/4 | 16112-S | 4 | 9/32 | .032 | 3/4 | 100 | 500 | 16 |



HEAVY SERIES

| | | | | | | | | |
|------|---------|---|------|------|-----|-----|------|----|
| 1/4 | 17101-S | 4 | 9/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 5/16 | 17102-S | 4 | 9/32 | .062 | 5/8 | 100 | 1000 | 26 |
| 3/8 | 17103-S | 4 | 9/32 | .062 | 5/8 | 100 | 1000 | 28 |
| 1/2 | 17105-S | 4 | 9/32 | .062 | 5/8 | 100 | 1000 | 33 |
| 5/8 | 17108-S | 4 | 9/32 | .062 | 3/4 | 100 | 500 | 23 |
| 3/4 | 17112-S | 4 | 9/32 | .062 | 3/4 | 100 | 500 | 26 |

VICTOR "SNAP ON" ALUMINUM CLAMPS

FOR HEAVY WALL CONDUIT (RIGID)

| CONDUIT SIZE (RIGID) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | |
|-------|---------|---|------|------|-----|-----|------|----|
| 1/2 | 14413-A | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 10 |
| 3/4 | 14414-A | 3 | 9/32 | .062 | 3/4 | 100 | 500 | 8 |
| 1 | 14415-A | 3 | 9/32 | .093 | 3/4 | 50 | 500 | 14 |
| 1 1/4 | 14416-A | 3 | 9/32 | .093 | 3/4 | 50 | 250 | 9 |



HEAVY SERIES

| | | | | | | | | |
|-------|---------|---|-------|------|-------|-----|-----|----|
| 1/2 | 14713-A | 4 | 9/32 | .093 | 3/4 | 100 | 500 | 11 |
| 3/4 | 14714-A | 4 | 9/32 | .093 | 3/4 | 100 | 500 | 13 |
| 1 | 14715-A | 4 | 13/32 | .125 | 1 | 50 | 250 | 15 |
| 1 1/4 | 14716-A | 4 | 13/32 | .125 | 1 | 25 | 125 | 10 |
| 1 1/2 | 14717-A | 4 | 13/32 | .125 | 1 | 25 | 125 | 11 |
| 2 | 14718-A | 4 | 13/32 | .125 | 1 1/2 | - | 50 | 8 |



VICTOR "SNAP ON" ALUMINUM CLAMPS

FOR THIN WALL CONDUIT (E.M.T.)

| CONDUIT SIZE (E.M.T.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|-----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|-----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|------|----|
| 1/2 | 14443-A | 4 | 9/32 | .062 | 5/8 | 100 | 1000 | 8 |
| 3/4 | 14444-A | 4 | 9/32 | .062 | 5/8 | 100 | 1000 | 12 |
| 1 | 14445-A | 4 | 9/32 | .062 | 3/4 | 100 | 500 | 8 |



HEAVY SERIES

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|------|----|
| 1/2 | 14743-A | 4 | 9/32 | .093 | 3/4 | 100 | 1000 | 15 |
| 3/4 | 14744-A | 4 | 9/32 | .093 | 3/4 | 100 | 500 | 10 |
| 1 | 14745-A | 4 | 9/32 | .093 | 3/4 | 50 | 500 | 12 |

VICTOR COPPER PLATED CLAMPS

FOR COPPER TUBING


| TUBING DIA. (O.D.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

SLOTTED HOLE CLAMPS



| | | | | | | | | |
|------|----------|---|------------|------|-----|-----|------|----|
| 1/8 | 15095-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 12 |
| 3/16 | 15100-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 13 |
| 1/4 | 15101-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 16 |
| 5/16 | 15102-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 18 |
| 3/8 | 15103-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 20 |
| 1/2 | 15105-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 22 |
| 3/4 | 15107-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 29 |

SLOTTED HOLE DUPLEX CLAMPS



| | | | | | | | | |
|------|----------|---|------------|------|-----|-----|------|----|
| 3/16 | 15700-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 25 |
| 1/4 | 15701-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 29 |
| 5/16 | 15702-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 35 |
| 3/8 | 15703-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 1000 | 39 |
| 1/2 | 15705-SL | 4 | 7/32 X 1/2 | .062 | 5/8 | 100 | 500 | 23 |

VICTOR BRASS CLAMPS

FOR CABLE OR TUBING

| TUBING DIA. (O.D.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | |
|----------|---------|---|------|------|-----|-----|------|----|
| 1/8-3/16 | 17200-B | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 9 |
| 1/4 | 17201-B | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 10 |
| 5/16 | 17202-B | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 12 |
| 3/8 | 17203-B | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 15 |
| 7/16 | 17204-B | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 17 |
| 1/2 | 17205-B | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 20 |
| 9/16 | 17206-B | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 21 |
| 5/8 | 17208-B | 4 | 7/32 | .062 | 1/2 | 100 | 1000 | 22 |

WIDE SERIES



| | | | | | | | | |
|-------|---------|---|------|------|-----|-----|------|----|
| 1/4 | 14151-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 12 |
| 5/16 | 14152-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 15 |
| 3/8 | 14153-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 17 |
| 7/16 | 14154-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 19 |
| 1/2 | 14155-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 9/16 | 14156-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 5/8 | 14158-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 26 |
| 11/16 | 14160-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 3/4 | 14162-B | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 30 |

MIDGET SERIES



| | | | | | | | | |
|------|---------|---|-------|------|-----|-----|------|---|
| 1/8 | 11575-B | 2 | 13/64 | .032 | 3/8 | 100 | 1000 | 3 |
| 3/16 | 11580-B | 2 | 13/64 | .032 | 3/8 | 100 | 1000 | 3 |
| 1/4 | 11581-B | 2 | 13/64 | .032 | 3/8 | 100 | 1000 | 4 |
| 5/16 | 11582-B | 2 | 13/64 | .032 | 3/8 | 100 | 1000 | 4 |
| 3/8 | 11583-B | 2 | 13/64 | .032 | 3/8 | 100 | 1000 | 5 |

VICTOR PAD TYPE STEEL CLAMPS

(FITS STANDARD 3/8 HIGH X 3/4 DIA WELDING PADS*)



| CABLE DIAMETER | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|----------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
| 1/4 | 10101-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 13 |
| 5/16 | 10102-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 13 |
| 3/8 | 10103-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 15 |
| 7/16 | 10104-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 16 |
| 1/2 | 10105-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 16 |
| 9/16 | 10106-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 17 |
| 5/8 | 10108-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 18 |
| 11/16 | 10110-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 20 |
| 3/4 | 10112-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 13/16 | 10115-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 7/8 | 10120-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 15/16 | 10122-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 26 |
| 1 | 10125-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 28 |

*PADS ARE NOT INCLUDED



VICTOR "SNAP ON" STEEL STRAPS

FOR HEAVY WALL CONDUIT (RIGID)

| CONDUIT SIZE (RIGID) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|


STANDARD SERIES

| | | | | | | | | |
|-------|---------|---|-------|------|-----|-----|------|----|
| 1/8 | 10020-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 1/4 | 10021-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 3/8 | 10022-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 1/2 | 10023-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 35 |
| 3/4 | 10024-S | 1 | 9/32 | .062 | 5/8 | 50 | 500 | 21 |
| 1 | 10025-S | 1 | 9/32 | .062 | 5/8 | 50 | 500 | 22 |
| 1 1/4 | 10026-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 15 |
| 1 1/2 | 10027-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 17 |
| 2 | 10028-S | 1 | 9/32 | .062 | 5/8 | - | 100 | 8 |
| 2 1/2 | 10029-S | 1 | 11/32 | .093 | 3/4 | - | 50 | 9 |
| 3 | 10030-S | 1 | 11/32 | .093 | 3/4 | - | 50 | 11 |
| 3 1/2 | 10031-S | 1 | 11/32 | .093 | 3/4 | - | 50 | 11 |
| 4 | 10032-S | 1 | 11/32 | .093 | 3/4 | - | 50 | 11 |
| 5 | 10033-S | 1 | 11/32 | .093 | 3/4 | - | 20 | 7 |
| 6 | 10034-S | 1 | 11/32 | .093 | 3/4 | - | 20 | 8 |



SMALL HOLE SERIES

| | | | | | | | | |
|-------|---------|---|------|------|-----|-----|------|----|
| 1/8 | 19220-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 1/4 | 19221-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 3/8 | 19222-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 1/2 | 19223-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 35 |
| 3/4 | 19224-S | 4 | 7/32 | .062 | 5/8 | 100 | 500 | 20 |
| 1 | 19225-S | 4 | 7/32 | .062 | 5/8 | 50 | 500 | 22 |
| 1 1/4 | 19226-S | 4 | 7/32 | .062 | 5/8 | 50 | 250 | 15 |




HEAVY SERIES

| | | | | | | | | |
|-------|---------|---|-------|------|-----|-----|-----|----|
| 1/2 | 10723-S | 2 | 9/32 | .093 | 3/4 | 100 | 500 | 30 |
| 3/4 | 10724-S | 2 | 9/32 | .093 | 3/4 | 50 | 500 | 36 |
| 1 | 10725-S | 2 | 9/32 | .093 | 3/4 | 50 | 250 | 21 |
| 1 1/4 | 10726-S | 2 | 13/32 | .125 | 1 | - | 100 | 18 |
| 1 1/2 | 10727-S | 2 | 13/32 | .125 | 1 | - | 50 | 10 |
| 2 | 10728-S | 2 | 13/32 | .125 | 1 | - | 50 | 14 |
| 2 1/2 | 10729-S | 2 | 13/32 | .125 | 1 | - | 50 | 15 |
| 3 | 10730-S | 2 | 13/32 | .125 | 1 | - | 25 | 9 |
| 3 1/2 | 10731-S | 2 | 13/32 | .125 | 1 | - | 25 | 12 |
| 4 | 10732-S | 2 | 13/32 | .125 | 1 | - | 25 | 12 |
| 5 | 10733-S | 2 | 13/32 | .125 | 1 | - | 20 | 13 |
| 6 | 10734-S | 2 | 13/32 | .125 | 1 | - | 20 | 14 |

LIGHT WEIGHT SERIES

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|------|----|
| 1/4 | 10621-S | 2 | 7/32 | .032 | 5/8 | 100 | 1000 | 14 |
| 3/8 | 10622-S | 2 | 7/32 | .032 | 5/8 | 100 | 1000 | 18 |
| 1/2 | 10623-S | 2 | 7/32 | .032 | 5/8 | 100 | 1000 | 21 |
| 3/4 | 10624-S | 2 | 7/32 | .032 | 3/4 | 100 | 500 | 14 |
| 1 | 10625-S | 2 | 7/32 | .032 | 3/4 | 50 | 500 | 17 |



FOR "BX" CABLE

| | | | | | | | | |
|---------------------------------|---------|---|------|------|-----|-----|------|----|
| 14-3 TO 12-3 & 3/8 FLEX | 10605-S | 1 | 3/16 | .032 | 1/2 | 100 | 1000 | 11 |
| | 19205-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 12-4 to 10-4 & 3/8 SHELL GROUND | 11206-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 27 |





VICTOR "SNAP ON" STEEL STRAPS

FOR THIN WALL CONDUIT (E.M.T.)

| CONDUIT SIZE (E.M.T.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|-----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|-----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

STANDARD SERIES




| | | | | | | | | |
|-------|---------|---|-------|------|-----|-----|------|----|
| 1/2 | 10063-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 3/4 | 10064-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 20 |
| 1 | 10065-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 23 |
| 1 1/4 | 10066-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 14 |
| 1 1/2 | 10067-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 17 |
| 2 | 10068-S | 1 | 9/32 | .062 | 5/8 | - | 100 | 9 |
| 2 1/2 | 10029-S | 1 | 11/32 | .093 | 3/4 | - | 50 | 9 |
| 3 | 10030-S | 1 | 11/32 | .093 | 3/4 | - | 50 | 11 |
| 3 1/2 | 10031-S | 1 | 11/32 | .093 | 3/4 | - | 50 | 11 |
| 4 | 10032-S | 1 | 11/32 | .093 | 3/4 | - | 50 | 11 |

SMALL HOLE SERIES

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|------|----|
| 1/2 | 19263-S | 4 | 7/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 3/4 | 19264-S | 4 | 7/32 | .062 | 5/8 | 100 | 500 | 20 |
| 1 | 19265-S | 4 | 7/32 | .062 | 5/8 | 100 | 500 | 23 |

HEAVY SERIES



| | | | | | | | | |
|-------|---------|---|-------|------|-----|-----|-----|----|
| 1/2 | 10763-S | 2 | 9/32 | .093 | 3/4 | 100 | 500 | 26 |
| 3/4 | 10764-S | 2 | 9/32 | .093 | 3/4 | 50 | 500 | 31 |
| 1 | 10765-S | 2 | 13/32 | .125 | 1 | - | 100 | 16 |
| 1 1/4 | 10766-S | 2 | 13/32 | .125 | 1 | - | 50 | 10 |
| 1 1/2 | 10767-S | 2 | 13/32 | .125 | 1 | - | 50 | 11 |
| 2 | 10768-S | 2 | 13/32 | .125 | 1 | - | 50 | 12 |
| 2 1/2 | 10729-S | 2 | 13/32 | .125 | 1 | - | 50 | 15 |
| 3 | 10730-S | 2 | 13/32 | .125 | 1 | - | 25 | 9 |
| 3 1/2 | 10731-S | 2 | 13/32 | .125 | 1 | - | 25 | 12 |
| 4 | 10732-S | 2 | 13/32 | .125 | 1 | - | 25 | 12 |

LIGHTWEIGHT SERIES

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|------|----|
| 1/2 | 10663-S | 2 | 7/32 | .032 | 5/8 | 100 | 1000 | 18 |
| 3/4 | 10664-S | 2 | 7/32 | .032 | 5/8 | 100 | 500 | 12 |

VICTOR STEEL STRAPS

FOR TUBING AND CABLE



| TUBING DIA. (O.D.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
| 1/4 | 12101-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 17 |
| 5/16 | 12201-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 20 |
| 3/8 | 12301-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 7/16 | 11204-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 1/2 | 11205-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 9/16 | 11206-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 5/8 | 11208-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 29 |
| 11/16 | 11210-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 3/4 | 11212-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 33 |
| 13/16 | 11215-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 35 |
| 7/8 | 11220-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 18 |
| 15/16 | 11222-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 20 |
| 1 | 11225-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 20 |
| 1 1/4 | 11230-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 22 |

VICTOR STEEL STRAPS

FOR TUBING AND CABLE (CONT'D)


| TUBING DIA. (O.D.) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

TWO GANG STRAPS




| | | | | | | | | |
|-------|----------|---|------|------|-----|-----|------|----|
| 1/4 | *12102-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 20 |
| 5/16 | *12202-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 3/8 | *12302-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 7/16 | 11304-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 1/2 | 11305-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 9/16 | 11306-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 5/8 | 11308-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 16 |
| 11/16 | 11310-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 18 |
| 3/4 | 11312-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 21 |
| 13/16 | 11315-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 20 |
| 7/8 | 11320-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 21 |
| 15/16 | 11322-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 23 |
| 1 | 11325-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 25 |

THREE GANG STRAPS



| | | | | | | | | |
|-------|----------|---|------|------|-----|-----|------|----|
| 1/4 | *12103-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 5/16 | *12203-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 28 |
| 3/8 | *12303-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 29 |
| 7/16 | 11404-S | 2 | 9/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 1/2 | 11405-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 19 |
| 9/16 | 11406-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 21 |
| 5/8 | 11408-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 20 |
| 11/16 | 11410-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 22 |
| 3/4 | 11412-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 23 |
| 13/16 | 11415-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 23 |
| 7/8 | 11420-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 27 |
| 15/16 | 11422-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 28 |
| 1 | 11425-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 29 |

FOUR GANG STRAPS



| | | | | | | | | |
|-------|----------|---|------|------|-----|-----|------|----|
| 1/4 | *12104-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 5/16 | *12204-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 34 |
| 3/8 | *12304-S | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 36 |
| 7/16 | 11504-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 20 |
| 1/2 | 11505-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 21 |
| 9/16 | 11506-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 23 |
| 5/8 | 11508-S | 2 | 9/32 | .062 | 5/8 | 100 | 500 | 24 |
| 11/16 | 11510-S | 2 | 9/32 | .062 | 5/8 | 50 | 250 | 10 |
| 3/4 | 11512-S | 2 | 9/32 | .062 | 5/8 | 50 | 250 | 11 |
| 13/16 | 11515-S | 2 | 9/32 | .062 | 5/8 | 50 | 250 | 12 |
| 7/8 | 11520-S | 2 | 9/32 | .062 | 5/8 | 50 | 250 | 15 |
| 15/16 | 11522-S | 2 | 9/32 | .062 | 5/8 | 50 | 250 | 16 |
| 1 | 11525-S | 2 | 9/32 | .062 | 5/8 | 50 | 250 | 16 |

* NO BEND ON TOP SURFACE

VICTOR STEEL GANG STRAPS


FOR MULTIPLE LINES OF TUBING OR WIRE

(GANG STRAP AND BACK PLATE 1/16" THICK X 5/8" WIDE)

| GANG STRAP | | | | | | BACK PLATE | | | |
|-----------------|--------------------|-----------------|-----------------------------|----------------|-------------|--------------------|-----------------|----------------|-------------|
| NUMBER OF LINES | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE CTR. DISTANCE | PIECES PER BOX | LBS PER BOX | VICTOR PART NUMBER | PRICE LIST PAGE | PIECES PER BOX | LBS PER BOX |

1/4" TUBE DIA. WITH 9/32" DIA. MOUNTING HOLES

| | | | | | | | | | |
|----|---------|---|-------|-----|-----|---------|---|-----|-----|
| 1 | 12101-S | 3 | 1 | 100 | 1.7 | 12151-S | 3 | 100 | 1.6 |
| 2 | 12102-S | 3 | 1 1/4 | 100 | 2.0 | 12152-S | 3 | 100 | 1.8 |
| 3 | 12103-S | 3 | 1 1/2 | 100 | 2.2 | 12153-S | 3 | 100 | 2.3 |
| 4 | 12104-S | 3 | 1 3/4 | 100 | 2.5 | 12154-S | 3 | 100 | 2.8 |
| 5 | 12105-S | 3 | 2 | 100 | 2.7 | 12155-S | 3 | 100 | 3.0 |
| 6 | 12106-S | 3 | 2 1/4 | 100 | 3.5 | 12156-S | 3 | 100 | 3.1 |
| 7 | 12107-S | 3 | 2 1/2 | 100 | 3.5 | 12157-S | 3 | 100 | 3.1 |
| 8 | 12108-S | 3 | 2 3/4 | 100 | 3.6 | 12158-S | 3 | 100 | 3.5 |
| 9 | 12109-S | 3 | 3 | 100 | 4.0 | 12159-S | 3 | 100 | 3.6 |
| 10 | 12110-S | 3 | 3 1/4 | 100 | 4.3 | 12160-S | 3 | 100 | 4.0 |
| 11 | 12111-S | 3 | 3 1/2 | 100 | 4.5 | 12161-S | 3 | 100 | 4.2 |
| 12 | 12112-S | 3 | 3 3/4 | 100 | 4.7 | 12162-S | 3 | 100 | 4.7 |
| 13 | 12113-S | 3 | 4 | 100 | 5.0 | 12163-S | 3 | 100 | 4.8 |
| 14 | 12114-S | 3 | 4 1/4 | 100 | 5.1 | 12164-S | 3 | 100 | 5.3 |
| 15 | 12115-S | 3 | 4 1/2 | 100 | 5.2 | 12165-S | 3 | 100 | 5.4 |
| 16 | 12116-S | 3 | 4 3/4 | 100 | 5.6 | 12166-S | 3 | 100 | 6.0 |
| 17 | 12117-S | 3 | 5 | 100 | 5.9 | 12167-S | 3 | 100 | 6.2 |
| 18 | 12118-S | 3 | 5 1/4 | 100 | 6.1 | 12168-S | 3 | 100 | 6.4 |



1/4" TUBE DIA. WITH 7/32" DIA. MOUNTING HOLES

| | | | | | | | | | |
|----|---------|---|-------|-----|-----|---------|---|-----|-----|
| 1 | 13701-S | 3 | 1 | 100 | 1.6 | 13751-S | 3 | 100 | 1.6 |
| 2 | 13702-S | 3 | 1 1/4 | 100 | 1.8 | 13752-S | 3 | 100 | 1.8 |
| 3 | 13703-S | 3 | 1 1/2 | 100 | 2.2 | 13753-S | 3 | 100 | 2.0 |
| 4 | 13704-S | 3 | 1 3/4 | 100 | 2.5 | 13754-S | 3 | 100 | 2.2 |
| 5 | 13705-S | 3 | 2 | 100 | 2.7 | 13755-S | 3 | 100 | 2.5 |
| 6 | 13706-S | 3 | 2 1/4 | 100 | 3.0 | 13756-S | 3 | 100 | 2.8 |
| 7 | 13707-S | 3 | 2 1/2 | 100 | 3.3 | 13757-S | 3 | 100 | 3.0 |
| 8 | 13708-S | 3 | 2 3/4 | 100 | 3.6 | 13758-S | 3 | 100 | 3.4 |
| 9 | 13709-S | 3 | 3 | 100 | 3.9 | 13759-S | 3 | 100 | 3.7 |
| 10 | 13710-S | 3 | 3 1/4 | 100 | 4.1 | 13760-S | 3 | 100 | 3.9 |
| 11 | 13711-S | 3 | 3 1/2 | 100 | 4.4 | 13761-S | 3 | 100 | 4.0 |
| 12 | 13712-S | 3 | 3 3/4 | 100 | 4.7 | 13762-S | 3 | 100 | 4.4 |
| 13 | 13713-S | 3 | 4 | 100 | 5.0 | 13763-S | 3 | 100 | 4.8 |
| 14 | 13714-S | 3 | 4 1/4 | 100 | 5.1 | 13764-S | 3 | 100 | 4.9 |
| 15 | 13715-S | 3 | 4 1/2 | 100 | 5.2 | 13765-S | 3 | 100 | 5.1 |
| 16 | 13716-S | 3 | 4 3/4 | 100 | 5.6 | 13766-S | 3 | 100 | 5.4 |
| 17 | 13717-S | 3 | 5 | 100 | 5.6 | 13767-S | 3 | 100 | 5.7 |
| 18 | 13718-S | 3 | 5 1/4 | 100 | 6.2 | 13768-S | 3 | 100 | 5.9 |

3/8" TUBE DIA. WITH 9/32" DIA. MOUNTING HOLES


| | | | | | | | | | |
|---|---------|---|-------|-----|-----|---------|---|-----|-----|
| 2 | 12302-S | 3 | 1 1/2 | 100 | 2.5 | 12153-S | 3 | 100 | 2.3 |
| 3 | 12303-S | 3 | 1 7/8 | 100 | 2.9 | 12177-S | 3 | 100 | 2.4 |
| 4 | 12304-S | 3 | 2 1/4 | 100 | 3.0 | 12156-S | 3 | 100 | 3.1 |
| 5 | 12305-S | 3 | 2 5/8 | 100 | 3.5 | 12178-S | 3 | 100 | 3.1 |
| 6 | 12306-S | 3 | 3 | 100 | 4.0 | 12159-S | 3 | 100 | 3.6 |
| 7 | 12307-S | 3 | 3 3/8 | 100 | 4.5 | 12179-S | 3 | 100 | 4.1 |
| 8 | 12308-S | 3 | 3 3/4 | 100 | 4.8 | 12162-S | 3 | 100 | 4.7 |

1/2" TUBE DIA. WITH 9/32" DIA. MOUNTING HOLES

| | | | | | | | | | |
|---|---------|---|-------|-----|-----|---------|---|-----|-----|
| 2 | 12502-S | 3 | 1 3/4 | 100 | 2.8 | 12154-S | 3 | 100 | 2.8 |
| 3 | 12503-S | 3 | 2 1/4 | 100 | 3.4 | 12156-S | 3 | 100 | 3.1 |
| 4 | 12504-S | 3 | 2 3/4 | 100 | 3.8 | 12158-S | 3 | 100 | 3.5 |
| 5 | 12505-S | 3 | 3 1/4 | 100 | 4.4 | 12160-S | 3 | 100 | 4.0 |
| 6 | 12506-S | 3 | 3 3/4 | 100 | 5.2 | 12162-S | 3 | 100 | 4.7 |
| 7 | 12507-S | 3 | 4 1/4 | 100 | 5.4 | 12164-S | 3 | 100 | 5.3 |
| 8 | 12508-S | 3 | 4 3/4 | 100 | 6.0 | 12166-S | 3 | 100 | 6.0 |

VICTOR MIDGET STRAPS

(GANG STRAP AND BACK PLATE 1/16" THICK X 3/8" WIDE)



| GANG STRAP | | | | | | BACK PLATE | | |
|-----------------|--------------------|-----------------|-----------------------------|-------------------|----------------|--------------------|-------------------|----------------|
| NUMBER OF LINES | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE CTR. DISTANCE | PIECES PER CARTON | LBS PER CARTON | VICTOR PART NUMBER | PIECES PER CARTON | LBS PER CARTON |

1/8" TUBE DIA. WITH 13/64" DIA. MOUNTING HOLES

| | | | | | | | | |
|---|---------|---|---------|------|----|---------|------|----|
| 1 | 10181-S | 1 | 3/4 | 1000 | 7 | 10191-S | 1000 | 7 |
| 2 | 10182-S | 1 | 3/4 | 1000 | 8 | 10192-S | 1000 | 8 |
| 3 | 10183-S | 1 | 1 | 1000 | 9 | 10193-S | 1000 | 9 |
| 4 | 10184-S | 1 | 1 3/16 | 1000 | 10 | 10194-S | 1000 | 10 |
| 5 | 10185-S | 1 | 1 9/32 | 1000 | 11 | 10195-S | 1000 | 11 |
| 6 | 10186-S | 1 | 1 13/32 | 1000 | 12 | 10196-S | 1000 | 12 |

VICTOR LIGHT SERIES GANG STRAPS

GANG STRAP 1/32" THICK X 3/8" WIDE WITH 13/64" DIA. MOUNTING HOLES.
BACK PLATE 1/16" THICK X 1/2" WIDE WITH 7/32" DIA. MOUNTING HOLES.

| GANG STRAP | | | | | | BACK PLATE | | | |
|-----------------|--------------------|-----------------|-----------------------------|----------------|-------------|--------------------|-----------------|----------------|-------------|
| NUMBER OF LINES | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE CTR. DISTANCE | PIECES PER BOX | LBS PER BOX | VICTOR PART NUMBER | PRICE LIST PAGE | PIECES PER BOX | LBS PER BOX |

3/16" TUBE DIA.

| | | | | | | | | | |
|---|---------|---|--------|-----|-----|---------|---|-----|-----|
| 1 | 10600-S | 1 | 13/16 | 100 | 0.5 | 11600-S | 2 | 100 | 1.4 |
| 2 | 10830-S | 2 | 1 | 100 | 0.6 | 11603-S | 3 | 100 | 1.4 |
| 3 | 10870-S | 2 | 1 3/16 | 100 | 0.6 | 11870-S | 3 | 100 | 1.5 |
| 4 | 10910-S | 2 | 1 3/8 | 100 | 0.9 | 11871-S | 3 | 100 | 1.6 |
| 5 | 10950-S | 2 | 1 9/16 | 100 | 0.9 | 11872-S | 3 | 100 | 1.6 |

1/4" TUBE DIA.

| | | | | | | | | | |
|---|---------|---|-------|-----|-----|---------|---|-----|-----|
| 1 | 10601-S | 1 | 7/8 | 100 | 0.5 | 11601-S | 3 | 100 | 1.3 |
| 2 | 10831-S | 2 | 1 1/8 | 100 | 0.6 | 11831-S | 3 | 100 | 1.2 |
| 3 | 10871-S | 2 | 1 3/8 | 100 | 0.8 | 11871-S | 3 | 100 | 1.6 |
| 4 | 10911-S | 2 | 1 5/8 | 100 | 0.9 | 11911-S | 3 | 100 | 1.9 |
| 5 | 10961-S | 2 | 1 7/8 | 100 | 1.0 | 11961-S | 3 | 100 | 2.0 |
| 6 | 10971-S | 2 | 2 1/8 | 100 | 1.0 | 11913-S | 3 | 100 | 2.3 |
| 7 | 10981-S | 2 | 2 3/8 | 100 | 1.2 | 11981-S | 3 | 100 | 2.6 |
| 8 | 10991-S | 2 | 2 5/8 | 100 | 1.2 | 11991-S | 3 | 100 | 2.8 |

5/16" TUBE DIA.

| | | | | | | | | | |
|---|---------|---|--------|-----|-----|---------|---|-----|-----|
| 1 | 10602-S | 1 | 15/16 | 100 | 0.6 | 11602-S | 3 | 100 | 1.4 |
| 2 | 10832-S | 2 | 1 1/4 | 100 | 0.8 | 11832-S | 3 | 100 | 1.4 |
| 3 | 10872-S | 2 | 1 9/16 | 100 | 0.9 | 11872-S | 3 | 100 | 1.6 |
| 4 | 10912-S | 2 | 1 7/8 | 100 | 1.0 | 11961-S | 3 | 100 | 2.0 |

3/8" TUBE DIA.

| | | | | | | | | | |
|---|---------|---|-------|-----|-----|---------|---|-----|-----|
| 1 | 10603-S | 1 | 1 | 100 | 0.6 | 11603-S | 3 | 100 | 1.4 |
| 2 | 10833-S | 2 | 1 3/8 | 100 | 0.9 | 11871-S | 3 | 100 | 1.6 |
| 3 | 10873-S | 2 | 1 3/4 | 100 | 1.0 | 11873-S | 3 | 100 | 1.9 |
| 4 | 10913-S | 2 | 2 1/8 | 100 | 1.1 | 11913-S | 3 | 100 | 2.3 |

VICTOR STEEL STRAPS

FOR SERVICE ENTRANCE CABLE

| CABLE SIZE & DESCRIPTION | VICTOR PART NUMBER | PRICE LIST PAGE | A | B | D | T | W | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------------|--------------------|-----------------|---|---|---|---|---|----------------|-------------------|----------------|
|--------------------------|--------------------|-----------------|---|---|---|---|---|----------------|-------------------|----------------|

STANDARD SERIES

| | | | | | | | | | | |
|---------------|---------|---|---------|-------|------|------|-----|-----|------|----|
| 6-3 "UF" | 10074-S | 1 | 1 1/4 | 13/32 | 9/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 8-3 | 10078-S | 1 | 11/16 | 3/8 | 9/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 6-3 | 10052-S | 1 | 23/32 | 15/32 | 9/32 | .062 | 5/8 | 100 | 1000 | 28 |
| 6-2 & 8-1 | | | | | | | | | | |
| 4-3 | 10054-S | 1 | 7/8 | 17/32 | 9/32 | .062 | 5/8 | 100 | 1000 | 32 |
| 2-3 | 10055-S | 1 | 31/32 | 17/32 | 9/32 | .062 | 5/8 | 100 | 1000 | 33 |
| 2-2 & 4-1 | | | | | | | | | | |
| 2-3 | 10056-S | 1 | 1 | 5/8 | 9/32 | .062 | 5/8 | 100 | 1000 | 34 |
| 2-3 (OLD) | 10058-S | 1 | 1 1/16 | 11/16 | 9/32 | .062 | 5/8 | 100 | 1000 | 37 |
| 2/0-3 | 10060-S | 1 | 1 9/32 | 11/16 | 9/32 | .062 | 3/4 | 100 | 500 | 22 |
| 2/0-2 & 1-1 | | | | | | | | | | |
| 4/0-2 | 10061-S | 1 | 1 13/32 | 13/16 | 9/32 | .062 | 3/4 | 100 | 500 | 26 |
| 4/0-2 & 2/0-1 | 10062-S | 1 | 1 1/2 | 7/8 | 9/32 | .062 | 3/4 | 100 | 500 | 26 |

HEAVY SERIES

| | | | | | | | | | | |
|-----------|---------|---|---------|--------|------|------|-----|-----|------|----|
| 6-3 | 10752-S | 2 | 23/32 | 15/32 | 9/32 | .093 | 3/4 | 100 | 1000 | 47 |
| 6-2 & 8-1 | | | | | | | | | | |
| 4-3 | 10754-S | 2 | 7/8 | 17/32 | 9/32 | .093 | 3/4 | 100 | 500 | 25 |
| 2-3 | 10755-S | 2 | 31/32 | 17/32 | 9/32 | .093 | 3/4 | 100 | 500 | 30 |
| 2-2 & 4-1 | | | | | | | | | | |
| 2-3 | 10756-S | 2 | 1 | 5/8 | 9/32 | .093 | 3/4 | 100 | 500 | 31 |
| 2-3 (OLD) | 10758-S | 2 | 1 1/16 | 11/16 | 9/32 | .093 | 3/4 | 50 | 500 | 35 |
| 4/0-3 | 10761-S | 2 | 1 3/4 | 1 3/32 | 9/32 | .093 | 3/4 | 50 | 250 | 24 |
| 4/0-3 | 10762-S | 2 | 1 21/32 | 1 | 9/32 | .093 | 3/4 | 50 | 250 | 22 |

Sample straps are available to determine best fit.

VICTOR GANG STRAPS FOR METRIC TUBING

GANG STRAP AND BACK PLATE 0.2 CM THICK "X 1.6 CM WIDE WITH 9/32" DIA. MOUNTING HOLES.

| GANG STRAP | | | | | | BACK PLATE | | |
|-----------------|--------------------|-----------------|----------------------------------|-------------------|----------------|--------------------|-----------------|-------------------|
| NUMBER OF LINES | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE CTR. DISTANCE (cm) | PIECES PER CARTON | LBS PER CARTON | VICTOR PART NUMBER | PRICE LIST PAGE | PIECES PER CARTON |

10mm TUBING DIA.

| | | | | | | | | |
|---|---------|---|-----|------|----|---------|---|------|
| 1 | 16210-S | 4 | 2.9 | 1000 | 22 | 16250-S | 4 | 1000 |
| 2 | 16310-S | 4 | 3.9 | 1000 | 26 | 16350-S | 4 | 1000 |
| 3 | 16410-S | 4 | 4.9 | 1000 | 30 | 16450-S | 4 | 1000 |
| 4 | 16510-S | 4 | 5.9 | 1000 | 34 | 16550-S | 4 | 1000 |
| 5 | 16610-S | 4 | 6.9 | 1000 | 38 | 16650-S | 4 | 1000 |

12mm TUBING DIA.



| | | | | | | | | |
|---|---------|---|-----|------|----|---------|---|------|
| 1 | 16212-S | 4 | 3.1 | 1000 | 23 | 16252-S | 4 | 1000 |
| 2 | 16312-S | 4 | 4.3 | 1000 | 28 | 16352-S | 4 | 1000 |
| 3 | 16412-S | 4 | 5.5 | 1000 | 33 | 16452-S | 4 | 1000 |
| 4 | 16512-S | 4 | 6.7 | 1000 | 38 | 16552-S | 4 | 1000 |
| 5 | 16612-S | 4 | 7.9 | 1000 | 43 | 16652-S | 4 | 1000 |

VICTOR STEEL STRAPS

FOR SERVICE ENTRANCE CABLE

| CABLE SIZE & DESCRIPTION | VICTOR PART NUMBER | PRICE LIST PAGE | A | B | D | T | W | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------------|--------------------|-----------------|---|---|---|---|---|----------------|-------------------|----------------|
|--------------------------|--------------------|-----------------|---|---|---|---|---|----------------|-------------------|----------------|

SMALL HOLE SERIES



| | | | | | | | | | | |
|-------------|----------|---|--------|-------|------|------|-----|-----|------|----|
| 8-3 | 19278-S | 4 | 11/16 | 3/8 | 7/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 6-3 | 19252-S | 4 | 23/32 | 15/32 | 7/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 6-2 & 8-1 | | | | | | | | | | |
| 4-3 | 19254-S | 4 | 7/8 | 17/32 | 7/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 2-3 | 19256-S | 4 | 1 | 5/8 | 7/32 | .062 | 5/8 | 100 | 1000 | 32 |
| 2-3 (OLD) | 19258-S | 4 | 1 1/16 | 11/16 | 7/32 | .062 | 5/8 | 100 | 1000 | 37 |
| 12-2 & 14-2 | 10100-S# | 1 | 7/16 | 5/16 | 5/32 | .032 | 1/2 | 100 | 1000 | 10 |
| 12-2 & 14-2 | 10150-S+ | 1 | 19/32 | 11/32 | 5/32 | .032 | 1/2 | 100 | 1000 | 11 |
| 8-3 | 10678-S | 2 | 11/16 | 3/8 | 7/32 | .032 | 3/4 | 100 | 1000 | 18 |
| 6-3 | 10652-S | 2 | 23/32 | 15/32 | 7/32 | .032 | 3/4 | 100 | 1000 | 20 |
| 6-2 & 8-1 | | | | | | | | | | |
| 4-3 | 10654-S | 2 | 7/8 | 17/32 | 7/32 | .032 | 3/4 | 100 | 1000 | 21 |
| 2-3 | 10656-S | 2 | 1 | 5/8 | 7/32 | .032 | 3/4 | 100 | 500 | 12 |
| 2-3 (OLD) | 10658-S | 2 | 1 1/16 | 11/16 | 7/32 | .032 | 3/4 | 100 | 500 | 13 |
| 12-2 & 14-2 | 10050-S# | 1 | 15/32 | 9/32 | 9/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 12-3 & 14-3 | 10806-S* | 2 | 1/2 | 3/8 | 9/32 | .062 | 5/8 | 100 | 1000 | 20 |
| 12-2 & 14-2 | 10051-S+ | 1 | 9/16 | 11/32 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 12-3 & 14-3 | 19206-S* | 4 | 1/2 | 3/8 | 7/32 | .062 | 5/8 | 100 | 1000 | 20 |
| 12-2 & 14-2 | 19250-S# | 4 | 15/32 | 9/32 | 7/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 12-2 & 14-2 | 19251-S+ | 4 | 9/16 | 11/32 | 7/32 | .062 | 5/8 | 100 | 1000 | 25 |

* V SHAPED STRAP TAKES ROUND CABLE 3/8 TO 9/16 DIA.

TAKES P.V.C. CABLE

+ TAKES ROMEX CABLE


VICTOR "SNAP ON" ALUMINUM STRAPS


FOR SERVICE ENTRANCE CABLES

| CABLE SIZE | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
| 6-3 | 14452-A | 3 | 7/32 | .062 | 5/8 | 100 | 1000 | 11 |
| 4-3 | 14454-A | 3 | 7/32 | .062 | 5/8 | 100 | 1000 | 12 |
| 2-3 | 14456-A | 3 | 7/32 | .062 | 5/8 | 100 | 1000 | 13 |

VICTOR STEEL "STAND OFF" STRAPS

| TUBE SIZE 1/2-9/16 | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
| A=1" | 10296-S | 1 | 13/64 | .032 | 1/2 | 100 | 500 | 11 |
| A=1 1/2" | 10298-S | 1 | 13/64 | .032 | 1/2 | 50 | 500 | 14 |





VICTOR "SNAP ON" ALUMINUM STRAPS

| CONDUIT SIZE (RIGID) | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|----------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|

FOR HEAVY WALL CONDUIT (RIGID)

| | | | | | | | | |
|-------|---------|---|-------|------|-----|-----|------|----|
| 1/2 | 14423-A | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 14 |
| 3/4 | 14424-A | 3 | 9/32 | .062 | 5/8 | 100 | 500 | 9 |
| 1 | 14425-A | 3 | 9/32 | .062 | 5/8 | 50 | 500 | 11 |
| 1 1/4 | 14426-A | 3 | 9/32 | .062 | 5/8 | 50 | 250 | 5 |
| 1 1/2 | 14427-A | 3 | 9/32 | .062 | 5/8 | 50 | 250 | 6 |
| 2 | 14428-A | 3 | 9/32 | .062 | 5/8 | - | 100 | 3 |
| 2 1/2 | 14429-A | 3 | 11/32 | .093 | 3/4 | - | 50 | 3 |
| 3 | 14430-A | 3 | 11/32 | .093 | 3/4 | - | 50 | 4 |
| 3 1/2 | 14431-A | 3 | 11/32 | .093 | 3/4 | - | 50 | 4 |
| 4 | 14432-A | 3 | 11/32 | .093 | 3/4 | - | 50 | 5 |



FOR THIN WALL CONDUIT "E.M.T." EMT CONDUIT

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|------|----|
| 1/2 | 14463-A | 3 | 9/32 | .062 | 5/8 | 100 | 1000 | 10 |
| 3/4 | 14464-A | 3 | 9/32 | .062 | 5/8 | 100 | 500 | 7 |
| 1 | 14465-A | 4 | 9/32 | .062 | 5/8 | 100 | 500 | 8 |


FOR SERVICE ENTRANCE CABLES CABLE SIZE

| | | | | | | | | |
|-----|---------|---|------|------|-----|-----|------|----|
| 6-3 | 14452-A | 3 | 7/32 | .062 | 5/8 | 100 | 1000 | 11 |
| 4-3 | 14454-A | 3 | 7/32 | .062 | 5/8 | 100 | 1000 | 12 |
| 2-3 | 14456-A | 3 | 7/32 | .062 | 5/8 | 100 | 1000 | 13 |

VICTOR COPPER STRAPS


FOR TYPE "L" TUBING

| NOM. TUBE DIA. | ACTUAL O.D. | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|----------------|-------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
| 3/8 | 1/2 | 13605-CO | 3 | 13/64 | .032 | 1/2 | 100 | 1000 | 12 |
| 1/2 | 5/8 | 13608-CO | 3 | 7/32 | .032 | 5/8 | 50 | 500 | 10 |
| 5/8 | 3/4 | 13612-CO | 3 | 7/32 | .032 | 5/8 | 50 | 500 | 11 |
| 3/4 | 7/8 | 13614-CO | 3 | 7/32 | .032 | 5/8 | 50 | 500 | 12 |
| 1 | 1 1/8 | 13616-CO | 3 | 7/32 | .032 | 3/4 | 50 | 500 | 17 |



VICTOR BRASS STRAPS

| CABLE DIAMETER O.D. | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|---------------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
| 1/8 | 11445-B | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 4 |
| 3/16 | 11450-B | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 4 |
| 1/4 | 11451-B | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 5 |
| 5/16 | 11452-B | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 5 |
| 3/8 | 11453-B | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 6 |
| 7/16 | 11454-B | 2 | 5/32 | .032 | 3/8 | 100 | 1000 | 7 |
| 1/2 | 11455-B | 2 | 13/64 | .032 | 3/8 | 100 | 1000 | 12 |
| 5/8 | 11458-B | 2 | 13/64 | .032 | 5/8 | 50 | 500 | 10 |
| 3/4 | 11462-B | 2 | 13/64 | .032 | 5/8 | 50 | 500 | 11 |



VICTOR "PAD" TYPE STEEL STRAPS

(FITS STANDARD 3/8" HIGH X 3/4" DIA. WELDING PADS)

| CABLE DIAMETER | VICTOR PART NUMBER | PRICE LIST PAGE | MOUNTING HOLE SIZE | MATERIAL THICKNESS | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|----------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|
|----------------|--------------------|-----------------|--------------------|--------------------|----------------|----------------|-------------------|----------------|


ONE GANG STRAPS

| | | | | | | | | |
|-------|----------|---|------|------|-----|-----|------|----|
| 1/4 | *10201-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 19 |
| 5/16 | *10202-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 20 |
| 3/8 | *10203-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 20 |
| 7/16 | 10204-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 1/2 | 10205-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 9/16 | 10206-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 5/8 | 10208-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 27 |
| 11/16 | 10210-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 28 |
| 3/4 | 10212-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 30 |
| 13/16 | 10215-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 7/8 | 10220-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 32 |
| 15/16 | 10222-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 33 |




TWO GANG STRAPS

| | | | | | | | | |
|-------|---------|---|------|------|-----|-----|------|----|
| 1/4 | 10301-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 5/16 | 10302-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 22 |
| 3/8 | 10303-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 7/16 | 10304-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 23 |
| 1/2 | 10305-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 25 |
| 9/16 | 10306-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 28 |
| 5/8 | 10308-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 31 |
| 11/16 | 10310-S | 1 | 9/32 | .062 | 5/8 | 100 | 1000 | 32 |
| 3/4 | 10312-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 17 |
| 13/16 | 10315-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 18 |
| 7/8 | 10320-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 20 |
| 15/16 | 10322-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 21 |



THREE GANG STRAPS

| | | | | | | | | |
|-------|----------|---|------|------|-----|-----|-----|----|
| 1/4 | *10401-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 13 |
| 5/16 | *10402-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 13 |
| 3/8 | *10403-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 14 |
| 7/16 | 10404-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 15 |
| 1/2 | 10405-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 16 |
| 9/16 | 10406-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 17 |
| 5/8 | 10408-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 19 |
| 11/16 | 10410-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 21 |
| 3/4 | 10412-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 22 |
| 13/16 | 10415-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 24 |
| 7/8 | 10420-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 25 |
| 15/16 | 10422-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 26 |



FOUR GANG STRAPS

| | | | | | | | | |
|-------|----------|---|------|------|-----|-----|-----|----|
| 1/4 | *10501-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 14 |
| 5/16 | *10502-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 15 |
| 3/8 | *10503-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 16 |
| 7/16 | 10504-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 17 |
| 1/2 | 10505-S | 1 | 9/32 | .062 | 5/8 | 100 | 500 | 19 |
| 9/16 | 10506-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 10 |
| 5/8 | 10508-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 11 |
| 11/16 | 10510-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 12 |
| 3/4 | 10512-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 13 |
| 13/16 | 10515-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 14 |
| 7/8 | 10520-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 14 |
| 15/16 | 10522-S | 1 | 9/32 | .062 | 5/8 | 50 | 250 | 15 |



PADS ARE NOT INCLUDED

* NO BEND ON TOP SURFACE

VICTOR PERFORATED STRIPS IN COIL


| VICTOR PART NUMBER | PRICE LIST PAGE | SIZE AND LENGTH OF PERFORATED STRIPS | HOLE SIZE | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|--------------------|-----------------|--------------------------------------|-----------|----------------|-------------------|----------------|
|--------------------|-----------------|--------------------------------------|-----------|----------------|-------------------|----------------|

COPPER

| | | | | | | |
|----------|------------|--------------------|--------|---|----|----|
| 11995-CO | ON REQUEST | 1/32" X 1/2" X 5' | 13/64" | 4 | 40 | 10 |
| 11998-CO | ON REQUEST | 1/32" X 3/4" X 10' | 9/32" | 2 | 20 | 9 |

GALVANEALD


| | | | | | | |
|---------|---|--------------------|--------|---|----|----|
| 10995-S | 2 | 1/32" X 1/2" X 5' | 13/64" | 4 | 40 | 10 |
| 10998-S | 2 | 1/32" X 3/4" X 10' | 9/32" | 2 | 20 | 13 |



VICTOR TUBING SUPPORTS

MADE OF .062 X 5/8 STEEL WITH 7/32 DIA. HOLES

| FOR 1/4" DIA. TUBE | | | | | FOR 3/8" DIA. TUBE | | | | |
|--------------------|--------------------|-----------------|----------------|-------------|--------------------|--------------------|-----------------|----------------|-------------|
| NUMBER OF TUBES | VICTOR PART NUMBER | PRICE LIST PAGE | PIECES PER BOX | LBS PER BOX | NUMBER OF TUBES | VICTOR PART NUMBER | PRICE LIST PAGE | PIECES PER BOX | LBS PER BOX |
| 2 | 18272-S | 4 | 100 | 2.2 | 2 | 18382-S | 4 | 100 | 2.2 |
| 3 | 18273-S | 4 | 100 | 3.4 | 3 | 18383-S | 4 | 100 | 3.4 |
| 4 | 18274-S | 4 | 100 | 3.6 | 4 | 18384-S | 4 | 100 | 4.4 |
| 5 | 18275-S | 4 | 100 | 3.8 | 5 | 18385-S | 4 | 100 | 5.2 |
| 6 | 18276-S | 4 | 100 | 4.0 | 6 | 18386-S | 4 | 100 | 6.0 |
| 7 | 18277-S | 4 | 100 | 4.2 | 7 | 18387-S | 4 | 100 | 6.8 |
| 8 | 18278-S | 4 | 100 | 4.8 | 8 | 18388-S | 4 | 100 | 7.6 |
| 9 | 18279-S | 4 | 100 | 5.2 | 9 | 18389-S | 4 | 100 | 8.4 |
| 10 | 18280-S | 4 | 100 | 6.5 | 10 | 18390-S | 4 | 50 | 4.6 |
| 11 | 18281-S | 4 | 50 | 3.6 | 11 | 18391-S | 4 | 50 | 4.8 |
| 12 | 18282-S | 4 | 50 | 4.0 | 12 | 18392-S | 4 | 50 | 5.0 |



VICTOR STEEL HANGERS

MADE OF .062 STEEL WITH 9/32 MOUNTING AND CLAMPING HOLES, EXCEPT AS NOTED,
AND ONE SQUARE HOLE FOR 1/4" CARRIAGE BOLT

| CABLE OR TUBE DIAMETER | HEAVY WALL CONDUIT (RIGID) | THIN WALL CONDUIT (EMT) | VICTOR PART NUMBER | PRICE LIST PAGE | MATERIAL WIDTH | PIECES PER BOX | PIECES PER CARTON | LBS PER CARTON |
|------------------------|----------------------------|-------------------------|--------------------|-----------------|----------------|----------------|-------------------|----------------|
|------------------------|----------------------------|-------------------------|--------------------|-----------------|----------------|----------------|-------------------|----------------|


WITHOUT NUTS & BOLTS

| | | | | | | | | |
|-----------|-----------|-------|-----------|---|-------|----|-----|----|
| 5/8 & 3/4 | 3/8 | 1/2 | 14200-S* | 3 | 3/4 | 50 | 500 | 23 |
| 1 | 1/2 & 3/4 | 3/4 | 14201-S * | 3 | 3/4 | 50 | 250 | 15 |
| 1 1/4 | 1 | 1 | 14202-S* | 3 | 3/4 | 25 | 250 | 16 |
| 1 1/2 | - | 1 1/4 | 14203-S | 3 | 3/4 | 25 | 250 | 23 |
| 1 3/4 | 1 1/4 | 1 1/2 | 14204-S | 3 | 3/4 | 25 | 125 | 15 |
| 2 | 1 1/2 | - | 14205-S | 3 | 1 | - | 50 | 7 |
| 2 1/2 | 2 | 2 | 14206-S# | 3 | 1 1/4 | - | 50 | 12 |
| 3 | 2 1/2 | 2 1/2 | 14207-S# | 3 | 1 1/4 | - | 50 | 14 |
| 3 1/2 | 3 | 3 | 14208-S# | 3 | 1 1/4 | - | 25 | 8 |
| 4 | 3 1/2 | - | 14209-S+ | 3 | 1 1/4 | - | 25 | 9 |
| 4 1/2 | 4 | - | 14210-S+ | 3 | 1 1/4 | - | 25 | 9 |




WITH NUTS & BOLTS ASSEMBLED

| | | | | | | | | |
|-----------|-----------|-------|----------|---|-------|---|-----|----|
| 5/8 & 3/4 | 3/8 | 1/2 | 18400-S* | 4 | 3/4 | - | 100 | 7 |
| 1 | 1/2 & 3/4 | 3/4 | 18401-S* | 4 | 3/4 | - | 100 | 8 |
| 1 1/4 | 1 | 1 | 18402-S* | 4 | 3/4 | - | 100 | 9 |
| 1 1/2 | - | 1 1/4 | 18403-S | 4 | 3/4 | - | 100 | 12 |
| 1 3/4 | 1 1/4 | 1 1/2 | 18404-S | 4 | 3/4 | - | 100 | 13 |
| 2 | 1 1/2 | - | 18405-S | 4 | 1 | - | 100 | 18 |
| 2 1/2 | 2 | 2 | 18406-S# | 4 | 1 1/4 | - | 50 | 13 |
| 3 | 2 1/2 | 2 1/2 | 18407-S# | 4 | 1 1/4 | - | 50 | 16 |
| 3 1/2 | 3 | 3 | 18408-S# | 4 | 1 1/4 | - | 25 | 9 |
| 4 | 3 1/2 | - | 18409-S+ | 4 | 1 1/4 | - | 25 | 10 |
| 4 1/2 | 4 | - | 18410-S+ | 4 | 1 1/4 | - | 25 | 11 |



WITH NUTS & CARRIAGE BOLTS ASSEMBLED

| | | | | | | | | |
|-----------|-----------|-------|-----------|-----|-------|---|-----|----|
| 5/8 & 3/4 | 3/8 | 1/2 | 18400-CB* | N/A | 3/4 | - | 100 | 7 |
| 1 | 1/2 & 3/4 | 3/4 | 18401-CB* | N/A | 3/4 | - | 100 | 8 |
| 1 1/4 | 1 | 1 | 18402-CB* | N/A | 3/4 | - | 100 | 9 |
| 1 1/2 | - | 1 1/4 | 18403-CB | N/A | 3/4 | - | 100 | 12 |
| 1 3/4 | 1 1/4 | 1 1/2 | 18404-CB | N/A | 3/4 | - | 100 | 13 |
| 2 | 1 1/2 | - | 18405-CB | N/A | 1 | - | 100 | 18 |
| 2 1/2 | 2 | 2 | 18406-CB# | N/A | 1 1/4 | - | 50 | 13 |
| 3 | 2 1/2 | 2 1/2 | 18407-CB# | N/A | 1 1/4 | - | 50 | 16 |
| 3 1/2 | 3 | 3 | 18408-CB# | N/A | 1 1/4 | - | 25 | 9 |
| 4 | 3 1/2 | - | 18409-CB+ | N/A | 1 1/4 | - | 25 | 10 |
| 4 1/2 | 4 | - | 18410-CB+ | N/A | 1 1/4 | - | 25 | 11 |




* MADE OF .048 STEEL.

25/64 DIAMETER MOUNTING HOLE SIZE.

+ 33/64 DIAMETER MOUNTING HOLE SIZE.


VICTOR GANG BOXES

1 5/8" DEEP, 4 1/2" WIDE, 1/2 & 3/4 CONCENTRIC KNOCKOUTS




| VICTOR PART NUMBER | LENGTH | CUBIC INCH CAPACITY | KNOCK - OUT SIDES | KNOCK- OUT ENDS | KNOCKOUT BOTTOM | | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|----------|---------------------|-------------------|-----------------|-----------------|------|------------------|--------------------|
| | | | | | 1/2" | 3/4" | | |
| VGB158-2 | 6 13/16 | 46.0 | 8 | 4 | 4 | 2 | 25 | 128 |
| VGB158-3 | 8 5/8 | 58.5 | 10 | 4 | 6 | 4 | 20 | 148 |
| VGB158-4 | 10 7/16 | 71.0 | 12 | 4 | 6 | 4 | 20 | 179 |
| VGB158-5 | 12 1/4 | 84.0 | 14 | 4 | 6 | 4 | 10 | 201 |
| VGB158-6 | 14 1/16 | 95.0 | 16 | 4 | 6 | 4 | 5 | 226 |
| VGB158-7 | 15 7/8 | 108.5 | 18 | 4 | 6 | 4 | 5 | 250 |
| VGB158-8 | 17 11/16 | 122.0 | 20 | 4 | 6 | 4 | 5 | 272 |
| VGB158-9 | 19 1/2 | 133.5 | 22 | 4 | 6 | 4 | 5 | 294 |

2 1/2" DEEP, 4 1/2" WIDE, 1/2 & 3/4 CONCENTRIC KNOCKOUTS




| VICTOR PART NUMBER | LENGTH | CUBIC INCH CAPACITY | KNOCK - OUT SIDES | KNOCK- OUT ENDS | KNOCKOUT BOTTOM | | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|----------|---------------------|-------------------|-----------------|-----------------|------|------------------|--------------------|
| | | | | | 1/2" | 3/4" | | |
| VGB212-2 | 6 13/16 | 71.0 | 8 | 4 | 4 | 2 | 25 | 180 |
| VGB212-3 | 8 5/8 | 90.5 | 10 | 4 | 6 | 4 | 20 | 220 |
| VGB212-4 | 10 7/16 | 111.8 | 12 | 4 | 6 | 4 | 20 | 260 |
| VGB212-5 | 12 1/4 | 128.7 | 14 | 4 | 6 | 4 | 10 | 290 |
| VGB212-6 | 14 1/16 | 148.2 | 16 | 4 | 6 | 4 | 5 | 320 |
| VGB212-7 | 15 7/8 | 169.5 | 18 | 4 | 6 | 4 | 5 | 360 |
| VGB212-8 | 17 11/16 | 188.8 | 20 | 4 | 6 | 4 | 5 | 390 |
| VGB212-9 | 19 1/2 | 208 | 22 | 4 | 6 | 4 | 5 | 420 |

2 1/2" DEEP, 4 1/2" WIDE, 3/4 & 1" CONCENTRIC KNOCKOUTS



| VICTOR PART NUMBER | LENGTH | CUBIC INCH CAPACITY | KNOCK - OUT SIDES | KNOCK- OUT ENDS | KNOCKOUT BOTTOM | | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|----------|---------------------|-------------------|-----------------|-----------------|------|------------------|--------------------|
| | | | | | 1/2" | 3/4" | | |
| VGB212-2-341 | 6 13/16 | 71.0 | 8* | 4 | 4 | 2 | 25 | 180 |
| VGB212-3-341 | 8 5/8 | 90.5 | 10* | 4 | 6 | 4 | 20 | 220 |
| VGB212-4-341 | 10 7/16 | 111.8 | 12* | 4 | 6 | 4 | 20 | 260 |
| VGB212-5-341 | 12 1/4 | 128.7 | 14* | 4 | 6 | 4 | 10 | 290 |
| VGB212-6-341 | 14 1/16 | 148.2 | 16* | 4 | 6 | 4 | 5 | 320 |
| VGB212-7-341 | 15 7/8 | 169.5 | 18* | 4 | 6 | 4 | 5 | 360 |
| VGB212-8-341 | 17 11/16 | 188.8 | 20* | 4 | 6 | 4 | 5 | 390 |
| VGB212-9-341 | 19 1/2 | 208 | 22* | 4 | 6 | 4 | 5 | 420 |


*FOUR OF THE SIDE KNOCKOUTS ARE 1/2" & 3/4", REMAINDER ARE 3/4" & 1"



VGB158-3 with Partitions VPTAB158-SQ


VICTOR GANG BOX COLLARS

1 5/8" DEEP, 4 1/2" WIDE, 1/2 & 3/4 CONCENTRIC KNOCKOUTS




| VICTOR PART NUMBER | LENGTH | CUBIC INCH CAPACITY | KNOCK - OUT SIDES | KNOCK-OUT ENDS | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|----------|---------------------|-------------------|----------------|------------------|--------------------|
| VCOLL158-2 | 6 13/16 | 46.0 | 8 | 4 | 25 | 84 |
| VCOLL158-3 | 8 5/8 | 58.5 | 10 | 4 | 20 | 96 |
| VCOLL158-4 | 10 7/16 | 71.0 | 12 | 4 | 20 | 110 |
| VCOLL158-5 | 12 1/4 | 84.0 | 14 | 4 | 10 | 122 |
| VCOLL158-6 | 14 1/16 | 95.0 | 16 | 4 | 5 | 134 |
| VCOLL158-7 | 15 7/8 | 108.5 | 18 | 4 | 5 | 146 |
| VCOLL158-8 | 17 11/16 | 122.0 | 20 | 4 | 5 | 160 |
| VCOLL158-9 | 19 1/2 | 133.5 | 22 | 4 | 5 | 171 |

2 1/2" DEEP, 4 1/2" WIDE, 1/2 & 3/4 CONCENTRIC KNOCKOUTS




| VICTOR PART NUMBER | LENGTH | CUBIC INCH CAPACITY | KNOCK - OUT SIDES | KNOCK-OUT ENDS | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|----------|---------------------|-------------------|----------------|------------------|--------------------|
| VCOLL212-2 | 6 13/16 | 71.0 | 8 | 4 | 25 | 124 |
| VCOLL212-3 | 8 5/8 | 90.5 | 10 | 4 | 20 | 143 |
| VCOLL212-4 | 10 7/16 | 111.8 | 12 | 4 | 20 | 161 |
| VCOLL212-5 | 12 1/4 | 128.7 | 14 | 4 | 10 | 180 |
| VCOLL212-6 | 14 1/16 | 148.2 | 16 | 4 | 5 | 196 |
| VCOLL212-7 | 15 7/8 | 169.5 | 18 | 4 | 5 | 215 |
| VCOLL212-8 | 17 11/16 | 188.8 | 20 | 4 | 5 | 232 |
| VCOLL212-9 | 19 1/2 | 208.0 | 22 | 4 | 5 | 252 |

2 1/2" DEEP, 4 1/2" WIDE, 3/4 & 1" CONCENTRIC KNOCKOUTS



| VICTOR PART NUMBER | LENGTH | CUBIC INCH CAPACITY | KNOCK - OUT SIDES | KNOCK-OUT ENDS | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|----------|---------------------|-------------------|----------------|------------------|--------------------|
| VCOLL212-2-341 | 6 13/16 | 71.0 | 8* | 4 | 25 | 124 |
| VCOLL212-3-341 | 8 5/8 | 90.5 | 10* | 4 | 20 | 143 |
| VCOLL212-4-341 | 10 7/16 | 111.8 | 12* | 4 | 20 | 161 |
| VCOLL212-5-341 | 12 1/4 | 128.7 | 14* | 4 | 10 | 180 |
| VCOLL212-6-341 | 14 1/16 | 148.2 | 16* | 4 | 5 | 196 |
| VCOLL212-7-341 | 15 7/8 | 169.5 | 18* | 4 | 5 | 215 |
| VCOLL212-8-341 | 17 11/16 | 188.8 | 20* | 4 | 5 | 232 |
| VCOLL212-9-341 | 19 1/2 | 208.0 | 22* | 4 | 5 | 252 |


*FOUR OF THE SIDE KNOCKOUTS ARE 1/2" & 3/4", REMAINDER ARE 3/4" & 1"



KNOCKOUT PATTERN FOR VCOLL212-4-341


VICTOR DEVICE COVERS

1/2" RISE




| VICTOR PART NUMBER | NUMBER OF GANGS | CUBIC INCH CAPACITY | DESCRIPTION | LENGTH | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|-----------------|---------------------|---------------------|----------|------------------|--------------------|
| VCOV12-2 | 2 | 8.1 | Fits 2 Gang Box | 7 | 20 | 48 |
| VCOV12-3 | 3 | 11.7 | Fits 3 & 2 Gang Box | 8 13/16 | 20 | 54 |
| VCOV12-4 | 4 | 14.9 | Fits 4 & 3 Gang Box | 10 5/8 | 10 | 60 |
| VCOV12-5 | 5 | 17.5 | Fits 5 & 4 Gang Box | 12 7/16 | 10 | 65 |
| VCOV12-6 | 6 | 20.4 | Fits 6 & 5 Gang Box | 14 1/4 | 5 | 70 |
| VCOV12-7 | 7 | 24.1 | Fits 7 & 6 Gang Box | 16 1/16 | 5 | 79 |
| VCOV12-8 | 8 | 26.9 | Fits 8 & 7 Gang Box | 17 7/8 | 5 | 95 |
| VCOV12-9 | 9 | 31.8 | Fits 9 & 8 Gang Box | 19 11/16 | 5 | 100 |

3/4" RISE



| VICTOR PART NUMBER | NUMBER OF GANGS | CUBIC INCH CAPACITY | DESCRIPTION | LENGTH | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|-----------------|---------------------|---------------------|----------|------------------|--------------------|
| VCOV34-2 | 2 | 11.2 | Fits 2 Gang Box | 7 | 20 | 55 |
| VCOV34-3 | 3 | 17.1 | Fits 3 & 2 Gang Box | 8 13/16 | 20 | 60 |
| VCOV34-4 | 4 | 21.6 | Fits 4 & 3 Gang Box | 10 5/8 | 10 | 70 |
| VCOV34-5 | 5 | 26.2 | Fits 5 & 4 Gang Box | 12 7/16 | 10 | 78 |
| VCOV34-6 | 6 | 30.5 | Fits 6 & 5 Gang Box | 14 1/4 | 5 | 86 |
| VCOV34-7 | 7 | 36.1 | Fits 7 & 6 Gang Box | 16 1/16 | 5 | 92 |
| VCOV34-8 | 8 | 41.3 | Fits 8 & 7 Gang Box | 17 7/8 | 5 | 104 |
| VCOV34-9 | 9 | 46.3 | Fits 9 & 8 Gang Box | 19 11/16 | 5 | 110 |

NO RISE DEVICE COVERS



| VICTOR PART NUMBER | NUMBER OF GANGS | DESCRIPTION | LENGTH | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|-----------------|---------------------|----------|------------------|--------------------|
| VCOVFD-2 | 2 | Fits 2 Gang Box | 7 | 20 | 39 |
| VCOVFD-3 | 3 | Fits 3 & 2 Gang Box | 8 13/16 | 20 | 45 |
| VCOVFD-4 | 4 | Fits 4 & 3 Gang Box | 10 5/8 | 10 | 51 |
| VCOVFD-5 | 5 | Fits 5 & 4 Gang Box | 12 7/16 | 10 | 56 |
| VCOVFD-6 | 6 | Fits 6 & 5 Gang Box | 14 1/4 | 5 | 62 |
| VCOVFD-7 | 7 | Fits 7 & 6 Gang Box | 16 1/16 | 5 | 68 |
| VCOVFD-8 | 8 | Fits 8 & 7 Gang Box | 17 7/8 | 5 | 74 |
| VCOVFD-9 | 9 | Fits 9 & 8 Gang Box | 19 11/16 | 5 | 79 |


TOGGLE SWITCH DEVICE COVERS



| VICTOR PART NUMBER | NUMBER OF GANGS | DESCRIPTION | LENGTH | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|-----------------|-----------------|----------|------------------|--------------------|
| VCOVTS-2 | 2 | Fits 2 Gang Box | 7 | 20 | 55 |
| VCOVTS-3 | 3 | Fits 3 Gang Box | 8 13/16 | 20 | 70 |
| VCOVTS-4 | 4 | Fits 4 Gang Box | 10 5/8 | 10 | 88 |
| VCOVTS-5 | 5 | Fits 5 Gang Box | 12 7/16 | 10 | 102 |
| VCOVTS-6 | 6 | Fits 6 Gang Box | 14 1/4 | 5 | 116 |
| VCOVTS-7 | 7 | Fits 7 Gang Box | 16 1/16 | 5 | 133 |
| VCOVTS-8 | 8 | Fits 8 Gang Box | 17 7/8 | 5 | 148 |
| VCOVTS-9 | 9 | Fits 9 Gang Box | 19 11/16 | 5 | 163 |


VICTOR DEVICE COVERS (CONT'D)

DUPLEX RECEPTACLE DEVICE COVERS




| VICTOR PART NUMBER | NUMBER OF GANGS | DESCRIPTION | LENGTH | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|-----------------|-----------------|----------|------------------|--------------------|
| VCOVDR-2 | 2 | Fits 2 Gang Box | 7 | 20 | 50 |
| VCOVDR-3 | 3 | Fits 3 Gang Box | 8 13/16 | 20 | 61 |
| VCOVDR-4 | 4 | Fits 4 Gang Box | 10 5/8 | 10 | 71 |
| VCOVDR-5 | 5 | Fits 5 Gang Box | 12 7/16 | 10 | 82 |
| VCOVDR-6 | 6 | Fits 6 Gang Box | 14 1/4 | 5 | 92 |
| VCOVDR-7 | 7 | Fits 7 Gang Box | 16 1/16 | 5 | 103 |
| VCOVDR-8 | 8 | Fits 8 Gang Box | 17 7/8 | 5 | 114 |
| VCOVDR-9 | 9 | Fits 9 Gang Box | 19 11/16 | 5 | 124 |

FLAT BLANK COVERS




| VICTOR PART NUMBER | NUMBER OF GANGS | DESCRIPTION | LENGTH | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|-----------------|-----------------|----------|------------------|--------------------|
| VCOVFL-2 | 2 | Fits 2 Gang Box | 7 | 20 | 60 |
| VCOVFL-3 | 3 | Fits 3 Gang Box | 8 13/16 | 20 | 75 |
| VCOVFL-4 | 4 | Fits 4 Gang Box | 10 5/8 | 10 | 92 |
| VCOVFL-5 | 5 | Fits 5 Gang Box | 12 7/16 | 10 | 104 |
| VCOVFL-6 | 6 | Fits 6 Gang Box | 14 1/4 | 5 | 123 |
| VCOVFL-7 | 7 | Fits 7 Gang Box | 16 1/16 | 5 | 137 |
| VCOVFL-8 | 8 | Fits 8 Gang Box | 17 7/8 | 5 | 154 |
| VCOVFL-9 | 9 | Fits 9 Gang Box | 19 11/16 | 5 | 169 |

GANG BOX ADAPTOR COVERS



| VICTOR PART NUMBER | DESCRIPTION | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|---------------|------------------|--------------------|
| VAC-1 | ADAPTOR COVER | 25 | 24 |

SQUARE BOX COVERS



| VICTOR PART NUMBER | DESCRIPTION | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|-----------------|------------------|--------------------|
| VFL-4000 | 4" SQUARE | 25 | 30 |
| VFL-41116 | 4 11/16" SQUARE | 25 | 42 |

GANG BOX PARTITIONS



| VICTOR PART NUMBER | DESCRIPTION | RISE | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|----------------------|------|------------------|--------------------|
| VPTAB158-SQ | Fits 1 5/8" Gang Box | NONE | 50 | 10.5 |
| VPTAB158-12 | Fits 1 5/8" Gang Box | 1/2" | 50 | 12.2 |
| VPTAB158-34 | Fits 1 5/8" Gang Box | 3/4" | 50 | 13.4 |
| VPTAB158-1 | Fits 1 5/8" Gang Box | 1" | 50 | 14.7 |
| VPTAB212-SQ | Fits 2 1/2" Gang Box | NONE | 50 | 16.6 |
| VPTAB212-12 | Fits 2 1/2" Gang Box | 1/2" | 50 | 17.0 |
| VPTAB212-34 | Fits 2 1/2" Gang Box | 3/4" | 50 | 19.6 |
| VPTAB212-1 | Fits 2 1/2" Gang Box | 1" | 50 | 20 |

CEILING BOX SUPPORTS



| VICTOR PART NUMBER | DESCRIPTION | STANDARD PACKAGE | LBS PER 100 PIECES |
|--------------------|---------------------|------------------|--------------------|
| C.B.S. BAR | CEILING BOX SUPPORT | 50 | 30 |

Victor Specialties stands for quality. Since 1943 Victor Specialties has been the Greatest Single Source for Clamps, Straps and Hangers.

Let us put our experience to work for you. We can satisfy your special part requirements. Just call or FAX for more information.

All Victor parts are zinc plated after fabrication to: ASTM-B-633 SC1 Type 1, unless otherwise noted.

Most Victor parts can be made in stainless steel.

TERMS AND CONDITIONS

- TERMS ARE 2% 10 DAYS NET 30 DAYS, F.O.B. OUR PLANT BRONX, NY. NO DISCOUNT ALLOWED ON FREIGHT.
- WE ACCEPT VISA, AMERICAN EXPRESS, DISCOVER CARD AND MASTERCARD
- FULL FREIGHT WILL BE PAID BY VICTOR SPECIALTIES ON ANY ONE SHIPMENT TO ONE DESTINATION IN THE U.S.A., EXCLUDING ALASKA AND HAWAII, ON ALL ORDERS VALUED AT \$500 OR MORE. ALL PREPAID SHIPMENTS ARE ROUTED AT THE DISCRETION OF VICTOR SPECIALTIES.
- ORDERS RECEIVED BEFORE NOON FOR STOCK ITEMS WILL LEAVE OUR PLANT THE FOLLOWING DAY.
- PRICES SELDOM VARY FROM THOSE LISTED; HOWEVER, WE RESERVE THE RIGHT TO CHANGE PRICES OR MATERIAL WITHOUT NOTICE.
- WE WILL NOT ACCEPT ANY RETURN ITEM WITHOUT PRIOR WRITTEN APPROVAL.
- CLAMPS, STRAPS AND HANGERS ARE SOLD IN UNITS OF 100 PIECES UNLESS STATED OTHERWISE.
- OUR WARRANTY IS LIMITED. WE SHALL NOT BE LIABLE FOR ANY INJURY, LOSS OR DAMAGE, DIRECT OR CONSEQUENTIAL, ARISING OUT OF THE USE OR INABILITY TO USE ANY ITEM SOLD BY US. OUR ONLY OBLIGATION, IN LIEU OF ANY WARRANTIES EXPRESSED OR IMPLIED, IS TO REPLACE ANY ITEM PROVED TO BE DEFECTIVE. BEFORE USING, THE USER SHOULD DETERMINE THE SUITABILITY OF THE PRODUCT FOR ITS INTENDED USE AND THE USER ASSUMES ALL RISK IN CONNECTION THEREWITH.
- ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED.
- WE CAN PROVIDE SHAPES, SIZES AND MATERIALS ADDITIONAL TO THOSE SHOWN IN THIS CATALOG. PLEASE CONTACT US FOR PRICE AND DELIVERY.
- FOR NON-CATALOG ITEMS, THERE IS A SETUP CHARGE OF \$75.00 FOR RUNS OF LESS THAN 1000 PIECES.
- SETUP CHARGES ARE NOT DISCOUNTED.
- MINIMUM BILLING IS \$50.00 PER INVOICE.



VICTOR SPECIALTIES

1350 GARRISON AVE. BRONX, NEW YORK 10474

(718) 893-2763 FAX (800) 221-3932

EST. 1943





**CLAMPS, STRAPS AND HANGERS
CAN ALSO BE MANUFACTURED IN
STAINLESS STEEL**



VICTOR SPECIALTIES
1350 GARRISON AVE. BRONX, NEW YORK 10474
(718) 893-2763 FAX (800) 221-3932

email: sales@victorsp.com

VISIT OUR WEBSITE AT www.victorspecialties.com