



SWITCHES
WIRE MARKER
SPLIT BOLTS
Mechanical
24 Hour
WIRE CONNECTORS
TERMINALS
ELECTRICAL TIES
WIRE CONNECTORS
MECHANICAL LUGS
ELECTRICAL TIES
WIRE MARKER
SPLIT BOLTS
24 Hour
TERMINALS
MECHANICAL LUGS



TORK®

NSi Industries LLC Huntersville, North Carolina

From its start in 1975, NSi has established itself as a leading supplier and innovator of unique connectors and wire management products. Today, we are one of the most trusted U.S. suppliers of quality tools, wire management essentials and high-quality timer products to over 5000 commercial, industrial, and residential contractors as well as thousands of homeowners throughout North America.

With facilities in Huntersville, North Carolina and Mount Vernon, New York, NSi provides centrally located distribution to its customers. We maintain inventories at levels conducive to complete on-time deliveries, we have earned reputable status for our quick delivery program enhanced by electronic ordering, order tracking, demand forecasting and electronic invoicing.

The selection of NSi residential electrical products and TORK timers in this catalog represents the perfect selection for any retailer. The offering has been carefully designed to deliver the highest turns and ROI in any store environment.

All of our products are warranted and backed by UL and CSA certification for safety and quality. We feel that our retail packaging is the best available, including features such as, in-use photos, simple icons, and sensible instructions. QR codes can be found on many products which are tied to additional instructions and even how-to videos. Wherever possible, we have made our product packaging smaller than our competition to give you more sales per square foot. All of our packages re-closable so customers can store unused product neatly in a toolbox or drawer.

Our company goal is to keep our products and packaging innovative and our policies customer-friendly. We strive to offer extraordinary service on a daily basis.

From the NSi team to you, good selling and thank you for supporting us.



LISTED



TABLE OF CONTENTS

EASY-TWIST™ WIRE CONNECTORS

Easy-Twist™ Standard Wire Connectors	7
Easy-Twist™ Winged Wire Connectors	8
Push-In Wire Connectors	9
Crimp Connectors	10
Closed end Connectors	10

GROUNDING ACCESSORIES

Grounding Wing Connector	9
Grounding Screws	10
Grounding Pigtails	10
Grounding Box Clips	10
Ground Rod Clamp	10
Waterpipe Ground Rod Clamp	10

SPLIT BOLTS AND MECHANICAL LUGS

Copper Split Bolts	11
Aluminum Split Bolts	11
Aluminum Mechanical Lugs	11
Copper Mechanical Lugs	11
Aluminum Splicer/Reducers	11
Aluminum Anti-Oxidant	11

MINITERMS SOLDERLESS TERMINALS

Rings	13
Spades	13
Butt Splices	14
Disconnects	14
Barrel Insulated Disconnects	14
Fully Insulated Disconnects	14
Waterproof Terminals	15
Tap Splices	15
Terminal Blocks	15
Terminal Kits, Wire Connector Kits	16

BATTERY CLAMPS AND CHARGING CLIPS

Battery Clamps	17
Charging Clips	17
Alligator Clips	17
Wall Plate Screws	17

REPLACEMENT SWITCHES

Toggles	19
Pushbuttons	20
Pull Chains	19
Rockers	20
Rotaries	20
Cord	20

CONDUIT FISHING/BENDING

Fish Tapes	23
Wire Lube	23
Conduit Benders	23
Bender Handles	23

HAND TOOLS

Wire Strippers	25
Automatic Wire Stripper	26
5 Function Tool	26
Cable Jacket Ripper	26
Cutters and Crimpers	27
Pliers	28
Screwdriver Set	28

MULTITESTERS

Analog	31
Digital	32

VOLTAGE TESTERS

Probes	33
Continuity Testers	34
Heavy-Duty Solenoid Tester	34
Receptacle Analyzers	35
Heavy-Duty Non-contact Tester	36
Battery Pocket Tester	36

CABLE TIES

Standard Locking	39
Outdoor/Ultraviolet Weather Resistant	39
Heavy-Duty	39
Fluorescent Colors	40
Assorted Colors	40
Mounting	40
Releasable	40
Beaded Releasable	41
Mounting Bases	41
Hook and Loop Strapping Ties	41
Stainless Steel	41
Stainless Steel Barb Ties	41
Cable Tie Tightening Tool	41
Cable Tie Canisters	42

WIRE MANAGEMENT

Low-Voltage Staples	45
Adjustable Ratchet Clamps	45
One-Hole Plastic Clamps	45
Assorted Rubber Hole Grommets	45
Coaxial - Plastic Staples	46
Coaxial - Metal Staples	46
Coaxial - Insulated Metal Staples	46
Spiral Wrap	47
Flex Tubing	47
Duct Seal	47
Circuit Breaker Markers	47
Heat Shrink Tubing	48
UF Splice Kits	48
Liquid Electrical Tape	48
NSi Ratchet Clamps	50

ELECTRICAL TAPE

Easy-Wrap™ Tape	49
Easy-Wrap™ Premium Tape	49
Color Assortment	49
Easy-Wrap™ Friction Tape	49
Silicone Wrapping Tape	49

TORK® nsi

Indoor, Outdoor, In-Wall Timers And Time Switches

Indoor Mechanical	55
Outdoor Mechanical	56
Indoor Digital	57
Outdoor Digital	58
Stake Timers	59
In-Wall Mechanical - A Series	61
In-Wall Mechanical - C Series	62
In-Wall Digital	63
In-Wall Countdown	64
1101B Series Time Switches	65
Water Heater Time Switch	66
Mechanical Universal Multi-Voltage Time Switch	67
Digital Universal Multi-Voltage Time Switch	68

PRODUCT SET-UP INFORMATION

INDEX BY PRODUCT NAME

INDEX BY PRODUCT NAME	87
-----------------------	----

INDEX BY MODEL NUMBER

INDEX BY MODEL NUMBER	91
-----------------------	----



NSI INDUSTRIES INTRODUCES A NEW FULL LINE OF WIRE MANAGEMENT, TOOLS, TESTERS, ELECTRICAL ACCESSORIES AND TIMERS. THE RIGHT MIX...AT THE RIGHT TIME.



From holiday to everyday,
Tork provides for every
timing need.

NSI Industries LLC • Huntersville, NC • USA
Phone 800.321.5847 • Fax 800.841.5566 • www.nsiindustries.com



NSI Industries LLC • Huntersville, NC • USA • Phone 800.321.5847 • Fax 800.841.5566 • www.nsiindustries.com

Wire Connectors

NSi Easy-Twist™ Wire Connectors, split bolts, mechanical lugs and grounding accessories are trusted and widely used by professional electricians for their exceptional design features.

UL and CSA listed to the highest standards and offered in multiple reusable packaging types, NSi connectors are engineered to superior material standards to accommodate a wide range of wire gauges and connection needs.



Easy-Twist™ Standard Wire Connectors

Professional quality screw-on wire connectors with features required by electricians.

- Color coded to industry standards.
- Square hardened internal spring “bites” into wires for secure connections.
- Flame-retardant thermoplastic shell with ribbed design for easy grip.
- Deep funnel entry to prevent flashover.
- For Copper to Copper connections.



Color	Model #	Pack	Pack Type	Wire Range
STANDARD WIRE CONNECTORS				
Grey	WC-G-14R	14	Clamshell	
Grey	WC-G-25R	25	Zip-Bag	22-14 AWG
Grey	WC-G-B	1000	Bulk-Bag	Max: 1 #16 w/1 #18 w/1 #20
Grey	WC-G-C	100	Box	Min: 2 #22
Grey	WC-G-SJ	300	Jar	300 volts max.
Blue	WC-B-14R	14	Clamshell	
Blue	WC-B-25R	25	Zip-Bag	22-14 AWG
Blue	WC-B-B	1000	Bulk-Bag	Max: 3 #16 Min: 2 #22
Blue	WC-B-C	100	Box	300 volts max.
Blue	WC-B-SJ	300	Jar	
Orange	WC-O-12R	12	Clamshell	
Orange	WC-O-25R	25	Zip-Bag	22-14 AWG
Orange	WC-O-B	500	Bulk-Bag	Max: 4 #16 w/1 #20
Orange	WC-O-C	100	Box	Min: 1 #18 w/1 #20
Orange	WC-O-CJ	100	Jar	600 volts max.
Yellow	WC-Y-9R	9	Clamshell	
Yellow	WC-Y-25R	25	Zip-Bag	22-10 AWG
Yellow	WC-Y-B	500	Bulk-Bag	Max: 1 #10 w/2#14 w/1 #16
Yellow	WC-Y-C	100	Box	Min: 3 #20
Yellow	WC-Y-CJ	100	Jar	600 volts max.
Red	WC-R-6R	6	Clamshell	
Red	WC-R-25R	25	Zip-Bag	22-10 AWG
Red	WC-R-B	500	Bulk-Bag	Max: 3 #10 Min: 3 #18
Red	WC-R-C	100	Box	600 volts max.
Red	WC-R-SJ	100	Jar	


ASSORTMENT PACKS				
WC-A-9R	9	Clamshell	(2) WC-G, WC-O (3) WC-Y (2) WC-R	
WC-A-25R	25	Zip-Bag	(3) WC-G (4) WC-B (6) WC-O, WC-Y, WC-R	
WC-AYR-160R	160	Jar	80 each: WC-R, WC-Y	

EASY-TWIST™ WIRE CONNECTORS



QR DATA
SCANNING TO SHOW
DETAILED WIRE
COMBINATIONS

DIMENSIONS (Inches)					
Color	A	B	C	D	E
Grey	.150	.264	.339	.228	.598
Blue	.161	.276	.386	.232	.693
Orange	.197	.390	.480	.307	.866
Yellow	.236	.441	.551	.311	.945
Red	.295	.511	.645	.360	1.04



Easy-Twist™ Wing Connectors

Professional quality screw-on winged wire connectors with expandable springs for wider wire ranges.

- Exceptional “wing” design increases torque force, making connections easier and faster.
- Square hardened internal spring “bites” into copper wires and then expands as wires are threaded, for greater range.
- Flame-retardant thermoplastic shell.
- For Copper to Copper connections.



Color	Model #	Pack	Pack Type	Wire Range
WING WIRE CONNECTORS				
Yellow	WWC-Y-6R	6	Clamshell	
Yellow	WWC-Y-25R	25	Zip-Bag	18-10 AWG
Yellow	WWC-Y-B	500	Bulk-Bag	Max: 2 #12 w/ 1 #14
Yellow	WWC-Y-C	100	Box	Min: 3 #18
Yellow	WWC-Y-CJ	100	Jar	600 volts/300 volt**
Red	WWC-R-6R	6	Clamshell	
Red	WWC-R-25R	25	Zip-Bag	18-8 AWG
Red	WWC-R-B	500	Bulk-Bag	Max: 5 #12 Solid Min: 3 #16
Red	WWC-R-C	100	Box	600 volts/300 volt**
Red	WWC-R-SJ	100	Jar	
Tan	WWC-T-6R	6	Clamshell	
Tan	WWC-T-25R	25	Zip-Bag	Increased Range
Tan	WWC-T-B	500	Bulk-Bag	22-8 AWG
Tan	WWC-T-C	100	Box	Max: 4 #12 Min: 3 #22 Solid
Tan	WWC-T-CJ	100	Jar	600 volts/300 volt**
Grey	WWC-G-6R	6	Clamshell	
Grey	WWC-G-25R	25	Zip-Bag	18-8 AWG
Grey	WWC-G-B	250	Bulk-Bag	Max: 3 #10 Min: 3 #14 w/ 1 #18
Grey	WWC-G-C	50	Box	600 volts max**
Grey	WWC-G-SJ	50	Jar	
Blue	WWC-B-2R	2	Clamshell	
Blue	WWC-B-10R	10	Zip-Bag	14-6 AWG
Blue	WWC-B-B	100	Bulk-Bag	Max: 3 #8 w/ 1 #12
Blue	WWC-B-C	50	Box	Min: 2 #10 w/ 1 #12
Blue	WWC-B-SJ	50	Jar	600 volts max**

ASSORTMENT PACKS


WWC-A-5R	5	Clamshell	(2) WWC-Y, WWC-R (1) WWC-G
WWC-A-25R	25	Zip-Bag	(8) WWC-Y, WWC-R (7) WWC-T (2) WWC-B
WWC-AYR-160R	160	Jar	80 each: WWC-R, WWC-Y

**Max: 600V (Building wire) 1000V (fixtures and signs)



QR DATA
SCANNING TO SHOW
DETAILED WIRE
COMBINATIONS

DIMENSIONS (Inches)					
Color	A	B	C	D	E
Grey	.394	.587	1.0	.394	1.31
Blue	.472	.740	1.26	.516	1.575
Tan	.283	.457	.720	.362	1.14
Yellow	.252	.386	.717	.354	1.01
Red	.354	.531	.906	.378	1.25



Easy-Twist™ Grounding Wing Connectors

For grounding connections in electrical boxes.

- Extra spring plating for ground purposes.
- Through-wire hole in top of connector allows single ground connection.
- Flame-retardant thermoplastic shell.
- For Copper to Copper connections.



Color	Model #	Pack	Pack Type	Wire Range
GROUNDING WING CONNECTORS				
Green	WWC-GR-6R	6	Clamshell	
Green	WWC-GR-25R	25	Zip-Bag	Green Grounding
Green	WWC-GR-B	500	Bulk-Bag	Wing Connector
Green	WWC-GR-C	100	Box	Max: 5 #12 min: 2 #14
Green	WWC-GR-SJ	100	Jar	

GROUNDING WIRING CONNECTOR

X System grounding wire

Y System grounding wire

Z "Through" wire between device and box ground


Note: If "through" wire is a jumper, be sure wire extends below skirt 6" min.

Push-In Wire Connectors

Color-coded push-in wire connectors with 22-12AWG solid and stranded wire range for quick non-twisting permanent connections.

Great flexibility in boxes and other tight spaces. Just strip the wire and insert the wire to complete the connection. One wire per opening ensures loose connections are eliminated. Available in 2, 3, 4 & 8 port configurations. Two blade construction holds wire securely.

- With clear construction for visual inspection.
- Flame: UL94V-2 flame retardant.
- Temperature extremes: 105°C (221°F).




Color	Model #	Pack	Pack Type	Wire Range
PUSH-IN WIRE CONNECTORS				
Yellow	PIWC-2-10R	10	Clamshell	2 PORT 22-12 AWG Solid & Stranded
Yellow	PIWC-2	100	Box	
Orange	PIWC-3-10R	10	Clamshell	3 PORT 22-12 AWG Solid & Stranded
Orange	PIWC-3	100	Box	
Clear	PIWC-4-10R	10	Clamshell	4 PORT 22-12 AWG Solid & Stranded
Clear	PIWC-4	100	Box	
Black	PIWC-8-5R	5	Clamshell	8 PORT 22-12 AWG Solid & Stranded
Black	PIWC-8	50	Box	

EASY-TWIST™ WIRE CONNECTORS

Steel Crimp and Nylon Pigtail Connectors

For permanent crimp-on, vibration-resistant, closed-end wire connections.



Model #	Pack	Pack Type	Specifications
STEEL CRIMP CONNECTORS			
Brass-plated steel construction		Dia: SB181-series: 13/64"	SB140-series: 17/64"
SB1810S-12R	12	Clamshell	18-10 AWG Steel
SB1810S	100	Clamshell	18-10 AWG Steel
SB1408S-8R	8	Clamshell	14-8 AWG Steel
SB1408S	100	Clamshell	14-8 AWG Steel
NYLON PIGTAIL CONNECTORS			
Tin-plated copper construction. Chemical resistant			
C22-N-10R	10	Clamshell	22-16 AWG
C16-N-10R	10	Clamshell	16-14 AWG
C12-N-8R	8	Clamshell	12-10 AWG

Grounding Accessories

Professional products for grounding wires in electrical boxes.



Model #	Pack	Pack Type	Specifications
GROUNDING SCREWS (Hex-head for ground wires)			
GSC-12R	12	Clamshell	Grounding screws 300V max, 75°C (167°F)
GSC	100	Clamshell	Grounding screws 300V max, 75°C (167°F)
GROUNDING PIGTAILS (Spade fork terminal and ground screw)			
PG12C-2R	2	Clamshell	Grounding pigtails 6.5 inches 12 AWG
PG 12 C	50	Bag	
GROUNDING CLIPS (Zinc Plated)			
GGC-1000-8R	8	Clamshell	Green Grounding clips For 10, 12, 14 AWG Wire
GGC-1000	100	Box	
GROUND ROD, ACORN TYPE CLAMPS (Cast Bronze)			
GRC-50R	1	Clamshell	1/2" Ground Rod Clamp
GRC-58R	1	Clamshell	5/8" Ground Rod Clamp
PIPE GROUND CLAMP (Zinc)			
GZ-1R	1	Clamshell	1/2" - 1" Water Pipe or Ground Rod Clamp Listed for direct burial

Split Bolts and Mechanical Lugs

High-strength solderless service connectors made of the highest quality copper and aluminum alloys for connection and splicing of heavy current-carrying copper, copperweld and aluminum wires and cables.



Model #	Pack	Pack Type	Wire Range
COPPER SPLIT BOLT CONNECTORS			
<i>Copper alloy for maximum conductivity. (High copper alloy for two maximum wire sizes.)</i>			
N-8R	2	Clamshell	16-8 AWG Stranded or Solid
N-6R	2	Clamshell	10-6 AWG Stranded or Solid
N-4R	2	Clamshell	8-4 AWG Solid
N-2R	2	Clamshell	6-2 AWG Solid
N-1/0R	1	Clamshell	4-0 AWG Stranded or Solid
N-2/0R	1	Clamshell	2-00 AWG Stranded or Solid
N-3/0R	1	Clamshell	2-000 AWG Stranded or Solid
COPPER SINGLE MECHANICAL LUGS			
<i>99.98% pure electrolytic copper. Plated screws.</i>			
DE703R	2	Clamshell	14-10 AWG 25A 1/8" Mtg. Hole
DE704R	2	Clamshell	14-6 AWG 35A 3/16" Mtg. Hole
DE705R	2	Clamshell	8-2 AWG 70A 1/4" Mtg. Hole
DE706R	2	Clamshell	6-1/0 AWG 125A 1/4" Mtg. Hole
ALUMINUM DUAL-RATED SPLIT BOLTS			
<i>Tin-plated aluminum. UL-486B listed for AL and CU combinations.</i>			
APS02R	1	Clamshell	8 -2 AWG Str/Str
APS11R	1	Clamshell	8 -1/0 AWG Str/Sol
APS21R	1	Clamshell	2 -2/0 AWG Str/Str
APS41R	1	Clamshell	6 -4/0 AWG Str/Str
ALUMINUM SPLICER/REDUCERS			
<i>For splicing two copper or aluminum wires of equal or different sizes. 6061T AL alloy. Tin-plated screws. 600V.</i>			
2-SRR	2	Clamshell	14-2 AWG
1/0-SRR	1	Clamshell	14 -1/0 AWG
4/0-SRR	1	Clamshell	6- 4/0 AWG
ALUMINUM MECHANICAL LUGS			
<i>Versatile and reusable set screw connectors. 6061T AL alloy. Tin-plated screws. For CU and AL conductors. 600V.</i>			
2TR	2	Clamshell	14-2 AWG 1/4" Mtg. Hole
2/0TR	2	Clamshell	14- 1/0 1/4" Mtg. Hole
ALUMINUM ANTI-OXIDANT			
<i>For retarding formation of AL oxide in AL to CU and AL connections. Helps minimize heat buildup.</i>			
OX-1-1R	1	Tube	Aluminum Anti-Oxidant 1 oz. Tube
OX-4	1	Tube	Aluminum Anti-Oxidant 4 oz. Tube

See www.nsiindustries.com for hundreds of additional mechanical connectors, terminal blocks, split bolts and compression connectors for most residential and commercial uses.



Ring and Spade Terminals

For Crimp-On Wire Connections

- For wire terminations on screw studs.
- Temperature range: 167°F (75°C).
- Rated at 600V max.
- Use NSi Crimp tool: NSi #NH-3.
- Vinyl Insulated Barrel




Model #	Pack	Pack Type	Wire Range
RING TERMINALS			
R22-6V-10R	10	Clamshell	Rings 22-18 AWG / 4-6 Stud
R22-8V-10R	10	Clamshell	Rings 22-18 AWG / 8-10 Stud
R22-6V-22R	22	Clamshell	Rings 22-18 AWG / 4-6 Stud
R22-8V-22R	22	Clamshell	Rings 22-18 AWG / 8-10 Stud
R16-6V-10R	10	Clamshell	Rings 16-14 AWG / 4-6 Stud
R16-8V-10R	10	Clamshell	Rings 16-14 AWG / 8-10 Stud
R16-14V-7R	7	Clamshell	Rings 16-14 AWG / 12-1/4" Stud
R16-6V-22R	22	Clamshell	Rings 16-14 AWG / 4-6 Stud
R16-8V-22R	22	Clamshell	Rings 16-14 AWG / 8-10 Stud
R16-14V-17R	17	Clamshell	Rings 16-14 AWG / 12-1/4" Stud
R16-6V-100R	100	Clamshell	Rings 16-14 AWG / 4-6 Stud
R16-8V-100R	100	Clamshell	Rings 16-14 AWG / 8-10 Stud
R16-14V-100R	100	Clamshell	Rings 16-14 AWG / 12-1/4" Stud
R12-8V-8R	8	Clamshell	Rings 12-10 AWG / 8-10 Stud
R12-14V-7R	7	Clamshell	Rings 12-10 AWG / 12- 1/4" Stud
R12-38V-7R	7	Clamshell	Rings 12-10 AWG / 1/4-3/8" Stud
R12-8V-14R	14	Clamshell	Rings 12-10 AWG / 8-10 Stud
R12-14V-14R	14	Clamshell	Rings 12-10 AWG / 12- 1/4" Stud
R12-38V-13R	13	Clamshell	Rings 12-10 AWG / 1/4-3/8" Stud
R12-8V-50R	50	Clamshell	Rings 12-10 AWG / 8-10 Stud
R12-14V-50R	50	Clamshell	Rings 12-10 AWG / 12- 1/4" Stud
SPADE TERMINALS			
S22-4V-10R	10	Clamshell	Spades 22-18 AWG / 4-6 Stud
S22-8V-7R	7	Clamshell	Spades 22-18 AWG / 8-10 Stud
S22-4V-20R	20	Clamshell	Spades 22-18 AWG / 4-6 Stud
S22-8V-20R	20	Clamshell	Spades 22-18 AWG / 8-10 Stud
S22-4V-100R	100	Clamshell	Spades 22-18 AWG / 4-6 Stud
S22-8V-100R	100	Clamshell	Spades 22-18 AWG / 8-10 Stud
S16-6V-10R	10	Clamshell	Spades 16-14 AWG / 4-6 Stud
S16-8V-10R	10	Clamshell	Spades 16-14 AWG / 8-10 Stud
S16-6V-20R	20	Clamshell	Spades 16-14 AWG / 4-6 Stud
S16-8V-20R	20	Clamshell	Spades 16-14 AWG / 8-10 Stud
S16-6V-100R	100	Clamshell	Spades 16-14 AWG / 4-6 Stud
S16-8V-100R	100	Clamshell	Spades 16-14 AWG / 8-10 Stud
S12-8V-8R	8	Clamshell	Spades 12-10 AWG / 8-10 Stud
S12-8V-50R	50	Clamshell	Spades 12-10 AWG / 8-10 Stud



MINITERMS SOLDERLESS TERMINALS

Disconnect Terminals and Butt Splices

- For joining wires in line.
- Rated at 600V max.
- Vinyl Insulated and Fully Insulated
- Temperature range: 167°F (75°C).
- Use NSi Crimp tool: NSi #NH-3.



Model #	Pack	Pack Type	Wire Range
FEMALE/MALE DISCONNECT TERMINALS (Barrel Insulated)			
F22-250-3V-10R	10	Clamshell	Disconnects Female 22-18 AWG 1/4" Tab
F22-250-3V-21R	21	Clamshell	Disconnects Female 22-18 AWG 1/4" Tab
F16-187-2V-10R	10	Clamshell	Disconnects Female 16-14 AWG 1/4" Tab
F16-187-2V-20R	20	Clamshell	Disconnects Female 16-14 AWG 1/4" Tab
F12-250-3V-8R	8	Clamshell	Disconnects Female 12-10 AWG 1/4" Tab
F12-250-3V-16R	16	Clamshell	Disconnects Female 12-10 AWG 1/4" Tab
M22-250-3V-10R	10	Clamshell	Disconnects Male 22-18 AWG 1/4" Tab
M22-250-3V-18R	18	Clamshell	Disconnects Male 22-18 AWG 1/4" Tab
M16-187-2V-10R	10	Clamshell	Disconnects Male 16-14 AWG 1/4" Tab
M16-187-2V-18R	18	Clamshell	Disconnects Male 16-14 AWG 1/4" Tab
M12-250-3V-8R	8	Clamshell	Disconnects Male 12-10 AWG 1/4" Tab
M12-250-3V-16R	16	Clamshell	Disconnects Male 12-10 AWG 1/4" Tab
P22-250-3V-50R	50	Clamshell	Disconnects 22-18 AWG Pairs
P16-187-2V-50R	50	Clamshell	Disconnects 16-14 AWG Pairs
P12-250-3V-50R	50	Clamshell	Disconnects 12-10 AWG Pairs
FEMALE/MALE DISCONNECT TERMINALS (Fully Insulated)			
IF22-250-3N-6R	6	Clamshell	Disconnects Female 22-18 AWG 1/4" Tab
IF22-250-3N-20PR	20	Clamshell	Disconnects 22-18 AWG Pairs
IF16-250-3N-6R	6	Clamshell	Disconnects Female 16-14 AWG 1/4" Tab
IF16-250-3N-20PR	20	Clamshell	Disconnects 16-14 AWG Pairs
IF12-250-3N-4R	4	Clamshell	Disconnects Female 12-10 AWG 1/4" Tab
IM22-250-3N-6R	6	Clamshell	Disconnects Male 22-18 AWG 1/4" Tab
IM16-250-3N-6R	6	Clamshell	Disconnects Male 16-14 AWG 1/4" Tab
IM12-250-3N-4R	4	Clamshell	Disconnects Male 12-10 AWG 1/4" Tab
P22-250-3N-50PR	50	Clamshell	Disconnects 22-18 AWG Pairs
P16-250-3N-50PR	50	Clamshell	Disconnects 16-14 AWG Pairs
P12-250-3N-30PR	30	Clamshell	Disconnects 12-10 AWG Pairs
PMF22-157N-10PR	10	Clamshell	Bullet Disconnects 22-16 AWG Pairs
PMF16-157N-20PR	20	Clamshell	Bullet Disconnects 16-14 AWG Pairs




Model #	Pack	Pack Type	Wire Range
BUTT SPLICE TERMINALS (600V/ Temp Range 167°F (75°C))			
B22-V-10R	10	Clamshell	Butt Splice 22-18 AWG
B22-V-100R	100	Clamshell	Butt Splice 22-18 AWG
B16-V-10R	10	Clamshell	Butt Splice 16-14 AWG
B16-V-50R	50	Clamshell	Butt Splice 16-14 AWG
B12-V-8R	8	Clamshell	Butt Splice 12-10 AWG
B12-V-50R	50	Clamshell	Butt Splice 12-10 AWG

Waterproof Crimp Terminals, Vinyl Insulated

Built with heat-activated, adhesive-lined shrink tubing for waterproof connections.

- Adhesive melts with torch or heat gun to create a water-tight seal.
- Impervious to chemicals, acid and salt water.
- Rated at 600V max.
- Temperature range: -67°F to 221°F (-55°C to 105°C).
- 2.5 to 1 shrink ratio.



Model #	Pack	Pack Type	Description/Wire Range
WATERPROOF CRIMP TERMINALS			
SR22-3R	3	Clamshell	Rings 22-18 AWG / 8-10 Stud- Waterproof
SS22-10-3R	3	Clamshell	Spades 22-18 AWG / 8-10 Stud- Waterproof
SB22-3R	3	Clamshell	Butt Splices 22-18 AWG - Waterproof
SR16-3R	3	Clamshell	Rings 16-14 AWG / 8-10 Stud- Waterproof
SS16-10-3R	3	Clamshell	Spades 16-14 AWG / 8-10 Stud- Waterproof
SB16-3R	3	Clamshell	Butt Splices- 16-14 AWG- Waterproof
SR12-3R	3	Clamshell	Rings 12-10 AWG / 8-10 Stud- Waterproof
SR12-14-3R	3	Clamshell	Rings 12-10 AWG / 1/4" Stud- Waterproof
SS12-10-3R	3	Clamshell	Spades 12-10 AWG / 8-10 Stud- Waterproof
SB12-3R	3	Clamshell	Butt Splices- 12-10 AWG- Waterproof
TAP SPLICES (600V Max.)			
Creates instant crimp-splicing of two wires without stripping insulation.			
PTC22-18-5R	5	Clamshell	Tap Splices 22-18 AWG
PTC22-18-15R	15	Clamshell	Tap Splices 22-18 AWG
PTC16-14-5R	5	Clamshell	Tap Splices 16-14 AWG
PTC16-14-15R	15	Clamshell	Tap Splices 16-14 AWG
PTC12-10-2R	5	Clamshell	Tap Splices 12-10 AWG



Model #	Pack	Pack Type	Description/Wire Range
TERMINAL BLOCKS - (30 Amp/600V)(22-10 AWG)(#8 Stud)			
TB3096-6	6	Box	Double Row Terminal Block - 6 POLE
TB3096-8	4	Box	Double Row Terminal Block - 8 POLE
TB3096-10	4	Box	Double Row Terminal Block - 10 POLE

MINITERMS SOLDERLESS TERMINALS

Terminal, Wire Connector and Tool Kits

Perfectly matched combination packages of the most commonly used terminal, wire connector and tool assortments.

- Merchandised in handy, storable reusable boxes and clamshells for tool boxes.
- Great for promotional sales.



Model #	Pack	Pack Type	Description/Wire Range
ASSORTED TERMINAL AND WIRE CONNECTOR KITS			
MTK-175	175	Box	175 Total Assorted Terminals
MTKL-100	100	Box	100 Total Assorted Terminals & Crimping Tool
MTKL-25	25	Clamshell	25 Total Assorted Terminals & Crimping Tool
MTK-2218	46	Clamshell	46 Total Assorted Terminals 22-18AWG
MTK-1614	48	Clamshell	48 Total Assorted Terminals 16-14 AWG
MTK-1210	28	Clamshell	28 Total Assorted Terminals 12-10 AWG
MTK-32	32	Clamshell	32 Total Assorted Terminals & Wire Connectors
MTK-80	80	Box	80 Total Assorted Terminals
ET-CP-12	180	Pail	(65) WC-O, (45) WC-Y, (30) WC-R, (40) WWC-T
ET-CP-13	185	Pail	(60) WC-O, (50) WWC-Y, (45) WWC-T, (30) WWC-R

MINITERMS SOLDERLESS TERMINALS



Clips and Clamps for testing every type of auto, marine, battery, and any other connection necessary.



Model #	Pack	Pack Type	Description
CHARGING CLIPS			
<i>For test equipment, batteries in 5A to 50A connections.</i>			
Non-Insulated spring action clips. Crimps to wire.			
BCL5-4R	4	Card	5 Amp
BCL10-4R	4	Card	10 Amp
BCL20-2R	2	Card	20 Amp
BCL30-2R	2	Card	30 Amp
BCL50-1R	1	Card	50 Amp
BATTERY CLAMPS (Insulated)			
<i>For battery connections.</i>			
Insulated positive/negative color-coded insulated handles. Copper clad.			
BCM10-2R	2	Card	10 Amp, 1 Red and 1 Black
BCM30-2R	2	Card	30 Amp, 1 Red and 1 Black
ALLIGATOR CLIPS			
<i>For auto, marine and test connections.</i>			
ATC-125-4R	4	Card	8-2 AWG Stranded
ATC-200-4R	4	Card	8-0 AWG Solid or Stranded
ATC-1B-2R	2	Card	2-00 AWG Stranded or Solid
ATC-2B-2R	2	Card	6-0000 AWG Stranded



Model #	Pack	Pack Type	Description
SWITCH PLATE SCREWS			
<i>Fits all standard switch plates and boxes. Color coded to match cover plates.</i>			
WPB-10R	10	Card	Brown Wall plate screws
WPI-10R	10	Card	Ivory Wall plate screws
WPW-10R	10	Card	White Wall plate screws

BATTERY CLAMPS AND LOW-VOLTAGE CLIPS

Switches

NSi accessory and replacement switch models include push-button, pull-chain, toggle, rotary, rocker, and in-line cord styles to replace original switches on hundreds of appliances and tools and to fit many special application needs. All NSi switches are UL and CSA listed and are engineered to provide the safest repetitive contact action.




SWITCHES SPLIT BOLTS WIRE MARKER WIRE CONNECTORS TERMINALS HEAT SHRINK CABLE TIES ELECTRICAL TAPE TESTERS GROUNDING MECHANICAL LUGS



Model #	Pack	Pack Type	Terminal Type	Specifications
TOGGLE SWITCHES				
<i>For large and small power tool, marine, automotive and machine application. 10A 277VAC / 20A 125VAC, 75C Max Temp Rating, 1/2" round Mtg. Hole.</i>				
78210TS	1	Clamshell	Screw	ON-OFF SPST 3/4 HP
78120TQ	1	Clamshell	Screw	ON-OFF SPST 3/4 HP
78200TS	1	Clamshell	Screw	ON-ON SPDT 3/4 HP
78150TS	1	Clamshell	Screw	ON-OFF SPST 3/4 HP
78160TS	1	Clamshell	Screw	ON-OFF-ON SPDT 3/4 HP
78220TS	1	Clamshell	Screw	ON-OFF DPST 1 1/2 HP
78270TS	1	Clamshell	Screw	ON-ON DPDT 1 1/2 HP
78230TS	1	Clamshell	Screw	ON-OFF-ON DPDT 1 1/2 HP
78015TS	1	Clamshell	Screw	ON-OFF SPST Insulated Outdoor
76065TS	1	Clamshell	Screw	3A 240VAC, 6A 125VAC ON-OFF SPST Bat Lever
78150TW	1	Clamshell	Screw	10A 125VAC, 8A 125VAC, 4A 250VAC ON-OFF SPST 1/3 HP
78130TS	1	Clamshell	Screw	3A 240VAC, 6A 125VAC ON-OFF SPST Short Ball



Model #	Pack	Pack Type	Terminal Type	Specifications
TOGGLE SWITCH BOOTS <i>Weather-resistant rubber covers allow toggle movement. Threaded housing screws onto casing of each toggle switch.</i>				
79300MSR	2	Clamshell	-	Toggle Switch Boots



Model #	Pack	Pack Type	Terminal Type	Specifications
PULL CHAIN SWITCHES				
<i>Single and multiple speed for fans and lamps. 13/16" mounting hole.</i>				
Single Speed				
75102CW	1	Clamshell	Pre-Wired	3A 125VL OFF-ON SPST- Nickel
75101CW	1	Clamshell	Pre-Wired	3A 125VL OFF-ON SPST- Brass
2-3 speed				
75110CW	1	Clamshell	Pre-Wired	OFF-ON-ON SPDT- Brass
75111CQ	1	Clamshell	Pre-Wired	6A 125VL OFF-ON-ON-ON SP3T- Brass




QR DATA SCANNING TO SHOW DETAILED WIRE DIAGRAMS


REPLACEMENT SWITCHES



Model #	Pack	Pack Type	Terminal Type	Specifications
PUSH BUTTON SWITCHES				
<i>ON-OFF action switches for household, power equipment or emergency shut-off applications. 1/2" Mounting hole</i>				
76010PW	1	Clamshell	Pre-Wired	Maintained Contact ON-OFF SPST 1/3HP 10A 125VAC, 8A 125VAC, 4A 250VAC
76065PS	1	Clamshell	Screw	Maintained Contact PUSH-ON SPST- Black Button 6A 120VAC, 3A 240VAC
76035PS	1	Clamshell	Screw	Maintained Contact PUSH-OFF SPST- Red Button 3A 120VAC, 1.5A 277VAC
76056PS	1	Clamshell	Spade	Maintained Contact ON-OFF SPST- Nickel 6A 125VAC, 3A 250VAC, 1A 125VT, 6A 125VL
76055PS	1	Clamshell	Pre-Wired	Maintained Contact ON-OFF SPST- Brass 6A 125VAC, 3A 250VAC, 1A 125VT, 6A 125VL



Model #	Pack	Pack Type	Terminal Type	Specifications
ROCKER SWITCHES				
<i>For household appliances and tools. 16A 125VAC / 8A 250VAC. .550" x 1.125" Mtg. hole required</i>				
77140RQ	1	Clamshell	Spade	Rocker ON-OFF SPST
<i>Lighted Rocker Switch</i>				
77150RQ	1	Clamshell	Spade	Rocker ON-OFF SPST- Lighted



Model #	Pack	Pack Type	Terminal Type	Specifications
ROTARY SWITCHES				
<i>For lights and appliances. 6A 125VAC / 3A 250VAC / 1A 125VT</i>				
77340RW	1	Clamshell	Pre-Wired	Rotary OFF-ON-ON SPST- Brass
77320RW	1	Clamshell	Pre-Wired	Rotary OFF-ON-ON-ON DP3T- Brass
CORD SWITCH - For lamp cords. 6A 125VAC / 3A 250VAC				
79100MS	1	Clamshell	Screw	ON-OFF SPST - Brown



QR DATA
SCANNING TO
SHOW DETAILED
WIRE DIAGRAMS



EASY-TWIST™

Easy-Twist™ Red winged wire connectors for 18-8AWG

Less time and less labor. That's why there's an Easy-Twist in over half a billion safe and secure connections.



It's easy on the hands and it's finger friendly. It grabs wires quickly. Fewer twists are needed to secure the wire.

Find out more about the engineering behind a twist. Easy-Twist™.

NSi Industries. Innovative Electrical Solutions Since 1975

9730 Northcross Center Ct. Huntersville, NC 28078
800.321.5847
www.nsiindustries.com



Conduit Bending & Fishing

NSi's wire fishing and conduit bending tools are widely used by professional electricians and homeowners for their quality and convenience. Our fish tapes are constructed using the toughest flat-wire spring steel and high-impact drop resistant housings. Our conduit benders are made from the highest-strength solid core lightweight aluminum alloy castings.



Fish Tapes

- Extremely flexible and durable spring steel.
- Looped end for attaching wires.
- Heavy-duty housing withstands rough conditions.
- High visibility yellow makes fish tape easy to locate.
- Viewing holes to show remaining tape.
- Handle slides along base to reel tape easily.
- 500 lb. maximum tape strength.



Model #	Pack	Description
PROFESSIONAL STEEL FISH TAPES		
FTS50	1	50' Steel Wire Fish Tape, Reel and Winder
FTS100	1	100' Steel Wire Fish Tape, Reel and Winder
UTILITY 25FT. FLAT WIRE FISH TAPE		
<i>For pulling electrical, low voltage, audio, video wires between walls, under carpets, over ceilings, between floors</i>		
Special wide, flat spring steel tape designed to fit under carpets and maneuver through tight areas Torpedo-style flat plastic tip to avoid catching on fabrics and insulation Easy to use housing with ring re-winder		
FTS25	1	25' Flat Spring Steel Wire Fish Tape
WIRE PULLING LUBRICANT		
<i>Applies to wires to lubricate wire pulling through conduits.</i>		
Exceptional lubricity. Retains higher lubricity when dry on cables. Compatible with all types of cable jackets. Retains original lubricity after re-wetting. Non-toxic to humans.		
SWL-1QR	1 Quart	Safe, Non-flammable, non-toxic Pulling Lubricant

Conduit Benders

- Light weight heat treated aluminum alloy.
- Clearly marked bending angles.
- Reinforced stress points.
- Levels on 3/4" and 1" bender models.



Model #	Pack	Description
CONDUIT BENDERS		
<i>For making precise bends in thinwall and rigid steel conduits.</i>		
CB50	1	For 1/2" Thinwall Conduit
CB75	1	For 3/4" Thinwall and 1/2" Rigid Conduit
CB100	1	For 1" Thinwall or 3/4" Rigid Conduit
CBH75	1	Rugged 38" Screw-on Bender Handle to Fit CB50 and CB75
CBH100	1	For use with CB100


Hand Tools

NSi wire strippers, cable cutters and electrical hand tools offer the essential and most widely used mix of products for residential and commercial electrical wireworking. Manufactured from drop forged, heat treated steel, NSi tools feature precision ground cutting edges and comfortable double-insulated handles. Exposed grips on all packaging lets customers feel the quality.



Precision Wire Strippers

- Finest heat-treated steel construction with precision-ground cutting edges.
- Double-Insulated cushioned handles.
- Strip solid or stranded copper or aluminum wires.




Model #	Pack	Description
ADJUSTABLE 10-24 AWG 5" WIRE STRIPPER		
TL-ADJ5	1	Adjustment wheel sets wire stripper for 8 wire gauge sizes from 10 to 24 AWG Wire cutter (CU/AL) Wire looper Heat treated steel Cushioned double insulated handle
10-20 AWG 6" WIRE STRIPPER		
TL-WS6	1	Wire Stripping Stations: 10, 12, 14, 16, 18, 20 AWG Pliers nose Wire cutter (CU/AL) Wire looper Spring and lock Heat treated steel Cushioned double insulated handle
10-20 AWG 8 1/2" 6-FUNCTION ELECTRICIAN'S TOOL		
TL-6-1	1	Wire Stripping Stations: 10, 12, 14, 16, 18, 20 AWG Pliers nose Wire cutter (CU/AL) Wire looper Insulated and non-insulated crimping stations Bolt cutter and re-threader Heat-treated steel Cushioned double insulated handle

Packed in clamshells with exposed handles so customers can feel the comfort-padded grips.



The essential multifunction wire strippers with comfort grips for comfortable, repetitive use.




Model #	Pack	Description
10-22 AWG 9 1/2" 5-FUNCTION ELECTRICIAN'S TOOL		
TL-5-1	1	Wire Stripping Stations: 10, 12, 14, 16, 18, 20, 22 AWG Wire cutter nose (CU/AL) Insulated and non-insulated crimping stations Bolt cutter and re-threader Heat-treated steel Cushioned double insulated handle
10-26 AWG 8 1/4" AUTOMATIC WIRE STRIPPER		
TL-AWS	1	One-squeeze action automatically adjusts to wire gauges from 10 to 26 AWG Wire cutter (CU/AL) Insulated and non-insulated crimping stations Spring return Heat-treated hardened steel Cushioned insulated handle
CABLE JACKET RIPPER 4"		
TL-RCR	1	Slits Non-Metallic jackets on building wire cables to allow individual stripping of internal wires Wire gauge measuring holes



Electrician's Hand Tools


- The essential hand tools for electrical work.
- Heat-treated drop-forged steel construction with precision ground edges for cutting copper and aluminum.
- Double-insulated cushioned handles.



Model #	Pack	Description
DIAGONAL CUTTING PLIERS 6 1/2"		
TL-DC	1	Designed and shaped for wire cutting in tight places Wire cutter nose (CU/AL) Heat-treated drop-forged steel Cushioned insulated handles
CABLE CUTTER 8"		
TL-CCIH	1	Designed for high-leverage cutting of cable to 2/0 (CU/AL) Heat-treated drop-forged steel Cushioned insulated handles
LONG REACH CUTTER/CRIMPER 8"		
TL-CRP	1	Long reach design for wire cutting and crimping in tight places Wire cutter nose (CU/AL) Heat-treated drop-forged steel Cushioned insulated handles

Packed in clamshells with exposed handles so customers can feel the comfort-padded grips.





Model #	Pack	Description
LONG NOSE PLIERS/STRIPPER/CRIMPER 6 1/2"		
TL-LNP	1	For long reach twisting and positioning wires in tight places Wire cutter (CU/AL) Non-insulated crimping stations Heat-treated drop-forged steel Cushioned insulated handles
LINEMAN'S PLIERS 7 1/2"		
TL-LP	1	Designed for high leverage pulling and twisting wires and cables Threaded wire-gripping nose Wire cutter (CU/AL) Heat-treated drop-forged steel Cushioned insulated handle
ELECTRICIAN'S 1000V SCREWDRIVERS		
TL-ISS	1	Fully insulated (1000 Volt) screwdriver set Comfort grip handles and fully insulated shafts for full shock protection (1) #2 Phillips head 8" (1) 3/16" slotted tip 8 1/4" Hang holes Heat treated drop forged steel



MINITERMS™

Designed for
MAX Strength and
made of the highest
quality material to
withstand tough
compression crimping.



NSi Industries. Innovative Electrical Solutions Since 1975

9730 Northcross Center Court, Huntersville, NC 28078
800.321.5847

www.nsiindustries.com



NSi Industries LLC • Huntersville, NC • USA • Phone 800.321.5847 • Fax 800.841.5566 • www.nsiindustries.com

Electrical Testers

Quality electrical testers are an essential part of every electrician's tool assortment and are vital to safe home installation of any electrical device. NSi offers a complete line of accurate and dependable UL and CSA-listed, double-insulated testers for home and commercial use. NSi's assortment includes circuit-probe testers for measuring low to high voltages, continuity and battery strength as well as a key assortment of highly accurate analog and digital multimeters.

WIRE MARKER
WIRE CONNECTORS
MECHANICAL LUGS
TESTERS
GROUNDING
WIRE
SWITCHES
SPLIT BOLTS
TERMINALS
HEAT SHRINK
CABLE TIES
ELECTRICAL TAPE
TOOL



Analog Multitesters

Precision analog meters for measuring voltage, amperage, continuity, resistance, battery and decibel strength.



Model #	Pack	Description
ANALOG MULTITESTER 5-FUNCTION 13 RANGE		
TES-MT12	1	Measures AC/DC voltage to 300 Volts DC amperage to 250 mA Decibels from -20 to 56dB 1.5 and 9V Batteries Continuity Fuse protection Insulated test leads Requires (2) AAA batteries
ANALOG MULTITESTER 7-FUNCTION 19 RANGE		
TES-MT19	1	Tests AC/DC voltage to check 10 Meg Decibels from -8 to +62dB 1.5 and 9V batteries Continuity with audible buzzer Fuse protection Insulated test leads Requires (2) AA batteries
ANALOG BATTERY TESTER		
TES-MTBTL	1	Tests AA; AAA; C; D; C; button cells; Ni-Cad; 3V lithium; 22.5V photo and lantern cells; 6V lantern; 12V, 15V photo cells. Insulated test leads Exclusive button cell test compartment

Packed in fully sealed clamshells



QR DATA
SCANNING TO
SHOW IN-USE
VIDEOS



Digital Multitesters

Precision digital meters for measuring voltage, amperage, continuity, resistance, battery and decibel strength.



Model #	Pack	Description
DIGITAL MULTITESTER 6-FUNCTION 20 RANGE		
TES-DT18	1	DC current to 200 mA 1.5 and 9V batteries Continuity (audible buzzer) Fuse protection Insulated test leads Requires 9V battery
500V DIGITAL AUTORANGING CLAMP-ON METER		
TES-DCM	1	DC current to 200 mV 3 1/2" display Low battery indicator Reads with no physical contact of wire Insulated test leads Requires (2) AAA batteries

Packed in fully sealed clamshells



QR DATA
SCANNING TO
SHOW IN-USE
VIDEOS

Circuit Probe Testers

Hand-held probe testers for measuring household voltage presence and strengths, low voltage, continuity and polarity.

- AC/DC home, commercial, automotive and marine voltages.




Model #	Pack	Description
80-250 VAC TWIN PROBE VOLTAGE TESTER		
TES-111	1	Neon light indicates presence of AC voltage from 80-250 VAC Double insulated housing and test leads Pocket clip
120 OR 240 VAC VOLTAGE TESTER		
TES-2	1	Dual neon light indicates presence of AC voltage of either 120 or 240 VAC Double insulated housing and test leads Pocket clip
5-50 VAC/DC VOLTAGE TESTER		
TES-LVT	1	Neon light indicates presence of low voltage from 5 to 50 VAC or DC Double insulated housing and fully insulated test leads with alligator clips Pocket clip

Packed in fully sealed clamshells



QR DATA SCANNING TO SHOW INSTRUCTIONS FOR USE



Model #	Pack	Description
CONTINUITY/VOLTAGE SCREWDRIVER TESTER		
TES-CT	1	Neon light indicates presence of AC voltage from 12-300 VAC Neon light also indicates circuit continuity Double insulated housing Handy screwdriver / voltage probe Pocket clip (2) LR-44 batteries included
120-480 VAC/DC HEAVY-DUTY VOLTAGE TESTER		
TES-SOL	1	Solenoid spring activated gauge measures voltage levels from 120 to 480 VAC Double insulated housing and heavy gauge 48" test leads with housing storage Lighted polarity indication



Packed in fully sealed clamshells



QR DATA
SCANNING
TO SHOW
INSTRUCTIONS
FOR USE

Circuit Probe Testers

Hand-held probe testers for measuring household voltage presence without contacting conductors, analyzing circuit wiring and GFCI integrity and quick battery testing.



Model #	Pack	Description
GFCI ELECTRICAL JUNCTION BOX WIRING ANALYZER		
TES-131	1	Plug in tester shows if wiring is correct in of electrical junction boxes Shows presence of up to six junction box wiring errors Includes push-button GFCI integrity test Neon bulb indication shows wiring accuracy code
ELECTRICAL JUNCTION BOX WIRING ANALYZER		
TES-122	1	Plug in tester shows if wiring is correct in of electrical junction boxes Shows presence of up to six junction box wiring errors Neon bulb indication shows wiring accuracy code
POINT PROBE CONTINUITY TESTER		
TES-CON	1	Neon bulb lights if continuity exists. 36" insulated test lead with alligator clip. Operates from (1) AAA batteries. Pocket clip
AUTOMOTIVE VOLTAGE TESTER		
TES-AUTO	1	Tests presence of voltage from 6-12 V . 36" test lead with alligator clamp. Pocket clip

Packed in fully sealed clamshells



QR DATA SCANNING TO SHOW INSTRUCTIONS FOR USE

VOLTAGE TESTERS

For quick and accurate circuit testing.



Model #	Pack	Description
90-200 VAC NON-CONTACT VOLTAGE TESTER		
TES-NC	1	<p>Detects household voltages from 90 to 200 VAC without touching conductors. Voltage presence is indicated by audible beeping and flashing light.</p> <p>(2) AAA batteries (included)</p> <p>Battery test feature included to ensure tester is working</p> <p>Pocket clip</p>
POCKET BATTERY TESTER		
TES-BT	1	<p>Checks strength and condition of AA, AAA, C, D, N, 9V and 1.5V Button Cell Batteries</p> <p>Flip up contact arm adjusts to battery poles</p>

Packed in fully sealed clamshells




QR DATA SCANNING TO SHOW INSTRUCTIONS FOR USE



EASY-TWIST™

Easy-Twist™ Tan winged wire connectors for 22-8 AWG



Less time and less labor. That's why there's an Easy-Twist in over half a billion safe and secure connections.

It's easy on the hands and it's finger friendly. It grabs wires quickly. Fewer twists are needed to secure the wire.

Find out more about the engineering behind a twist. Easy-Twist™.

NSi Industries. Innovative Electrical Solutions Since 1975

9730 Northcross Center Ct. Huntersville, NC 28078

    800.321.5847

www.nsiindustries.com



NSi Industries LLC • Huntersville, NC • USA • Phone 800.321.5847 • Fax 800.841.5566 • www.nsiindustries.com

Cable Ties


NSi's wide assortment of tough nylon cable ties provide hundreds of everyday bundling and fastening solutions. Offered in indoor and UV-treated outdoor zip-lock, releasable, heavy-duty super high strength, mounting, colored, fluorescent, beaded releasable and hook & loop varieties in multiple lengths, NSi cable ties are UL and CSA certified and far exceed industry standards for tensile strength. Each package is resealable for storage.



Cable Ties

Handy and versatile with thousands of uses including bundling wires, cables, cards, hoses, gear and more.


- Nylon 6/6, Meet UL94 V-2 flammability classification
- -40° to 85°C (-40° to 185°F)



Length	Color	Model #	Pack	Max. Bundle Diameter	Tensile Strength
STANDARD CABLE TIES					
Lengths from 4" to 14" to secure bundles up to 4 1/8".					
4"	White	418-40R	40	7/8"	18 lbs.
8"	White	840-20R	20	2 1/8"	40 lbs.
11"	White	1150-12R	12	3"	50 lbs.
14"	White	1450-8R	8	4 1/8"	50 lbs.
4"	White	418-100R	100	7/8"	18 lbs.
8"	White	840-100R	100	2 1/8"	40 lbs.
11"	White	1150-100R	100	3"	50 lbs.
14"	White	1450-100R	100	4 1/8"	50 lbs.
8"	White	850X	1000	2 1/8"	50 lbs.
11"	White	1150X	1000	3"	50 lbs.
UV BLACK TIES FOR INDOOR/OUTDOOR USE					
UV additive resists outdoor sunlight deterioration.					
4"	Black	4180-30R	30	7/8"	18 lbs.
8"	Black	8400-15R	15	2 1/8"	40 lbs.
11"	Black	11500-8R	8	3"	50 lbs.
14"	Black	14500-8R	8	4 1/8"	50 lbs.
4"	Black	4180-100R	100	7/8"	18 lbs.
8"	Black	8400-100R	100	2 1/8"	40 lbs.
11"	Black	11500-100R	100	3"	50 lbs.
14"	Black	14500-100R	100	4 1/8"	50 lbs.
8"	Black	8500X	1000	2 1/8"	50 lbs.
11"	Black	11500X	1000	3"	50 lbs.
HEAVY DUTY CABLE TIES					
HEAVY DUTY CABLE TIES					
For supporting larger, heavier bundles up to 175 pounds.					
15"	White	15120-10R	10	4 1/4"	120 lbs.
18"	White	18175-10R	10	5"	175 lbs.
21"	White	21175-10R	10	6 7/16"	175 lbs.
24"	White	24175-10R	10	7"	175 lbs.
36"	White	36175-10R	10	10 5/8"	175 lbs.
48"	White	48175-10	10	15"	175 lbs.
8"	White	8120	100	2 1/8"	120 lbs.
11"	White	11120	100	3"	120 lbs.
15"	White	14120	100	4 1/4"	120 lbs.
18"	White	18175	50	5"	175 lbs.
HEAVY DUTY UV BLACK TIES FOR INDOOR/OUTDOOR USE					
15"	Black	151200-10R	10	4 1/4"	120 lbs.
18"	Black	181750-10R	10	5"	175 lbs.
21"	Black	211750-10R	10	6 7/16"	175 lbs.
24"	Black	241750-10R	10	7"	175 lbs.
36"	Black	361750-10R	10	10 5/8"	175 lbs.
48"	Black	481750-10R	10	15"	175 lbs.
8"	Black	81200	100	2 1/8"	120 lbs.
11"	Black	111200	100	3"	120 lbs.
15"	Black	141200	100	4 1/4"	120 lbs.
18"	Black	181750	50	5"	175 lbs.

CABLE TIES

All NSi cable ties are packed in Zip-lock bags.



Length	Color	Model #	Pack	Max. Bundle Diameter	Tensile Strength
FLUORESCENT CABLE TIES					
Glow-Bright colors for easy identification.					
4"	Orange	418-16-25R	25	7/8"	18 lbs.
4"	Yellow	418-17-25R	25	7/8"	18 lbs.
4"	Green	418-18-25R	25	7/8"	18 lbs.
4"	Blue	418-20-25R	25	7/8"	18 lbs.
4"	Assorted	418-AFT	100	7/8"	18 lbs.
8"	Assorted	840-AFT	100	2 1/8"	50 lbs.
8"	Orange	750-16	100	2 1/8"	50 lbs.
8"	Yellow	750-17	100	2 1/8"	50 lbs.
8"	Green	750-18	100	2 1/8"	50 lbs.
8"	Blue	750-20	100	2 1/8"	50 lbs.
COLORED CABLE TIES					
For identification and separation. Great for home and garden use.					
8"	Brown	840-1	100	2 1/8"	40 lbs.
8"	Red	840-2	100	2 1/8"	40 lbs.
8"	Orange	840-3	100	2 1/8"	40 lbs.
8"	Yellow	840-4	100	2 1/8"	40 lbs.
8"	Green	840-5	100	2 1/8"	40 lbs.
8"	Blue	840-6	100	2 1/8"	40 lbs.
8"	Purple	840-7	100	2 1/8"	40 lbs.
8"	Grey	840-8	100	2 1/8"	40 lbs.
8"	Green	840-GR-20R	20	2 1/8"	40 lbs.
8"	Assorted	840-AST-20R	20	2 1/8"	40 lbs.
8"	Green	840-GR-100R	100	2 1/8"	40 lbs.
8"	Assorted	840-AST-100R	100	2 1/8"	40 lbs.
RELEASABLE CABLE TIES					
RELEASABLE CABLE TIES					
Trigger pawl allows for multiple time use.					
8"	White	850-R-25R	25	2 1/8"	50 lbs.
11"	White	1150-R-20R	20	3"	50 lbs.
8"	White	850R	100	2 1/8"	50 lbs.
11"	White	1050R	100	3"	50 lbs.
UV BLACK RELEASABLE CABLE TIES					
8"	Black	8500-R-25R	25	2 1/8"	50 lbs.
11"	Black	11500-R-20R	20	3"	50 lbs.
MOUNTING CABLE TIES					
MOUNTING CABLE TIES (FITS #10 WOOD SCREW)					
For mounting bundles to wood studs or walls. Mounting hole fits #10 wood screw. Indoor and outdoor ultraviolet black ties.					
8"	White	750MH-20R	20	2 1/8"	50 lbs.
8"	Black	7500MH-15R	15	2 1/8"	50 lbs.
8"	White	750MH-100R	100	2 1/8"	50 lbs.
8"	Black	7500MH-100R	100	2 1/8"	50 lbs.

Cable Ties

Handy and versatile with thousands of uses including bundling wires, cables, cards, hoses, gear and more.



Length	Color	Model #	Pack	Max. Bundle Diameter	Tensile Strength
BEADED CABLE TIES					
Releasable beaded design allows multiple time use. Great for garden and power tool cords.					
9"	Black	9700B-15R	15	2 1/2"	-
9"	Green	970BG-15R	15	2 1/2"	-
11"	Black	11700B-15R	15	3"	-
11"	Green	1170BG-15R	15	3"	-

Length	Color	Model #	Pack	Max. Bundle Diameter	Tensile Strength
HOOK AND LOOP TIES					
Releasable stick-to-itself hook & loop design allows multiple time use. Great for attaching gear and bundling power tool cords.					
8"	Black	V850-5R	5	2"	-
12"	Black	V1250-3R	3	3"	-

Length	Color	Model #	Pack	Max. Bundle Diameter	Tensile Strength
STAINLESS STEEL CABLE TIES					
Extremely heavy duty Grade 304 self-locking stainless steel ties for harsh outdoor and corrosive environments.					
6"	Silver	SS6100-10R	10	1 1/4"	100
11"	Silver	SS11100-10R	10	2 3/4"	100


Length	Color	Model #	Pack	Max. Bundle Diameter	Tensile Strength
STAINLESS STEEL BARB CABLE TIES					
With stainless steel barb embedded in pawl at 45 degree angle to set strap to any desired length in range.					
7.5"	White	750-SB	100	2"	50 lbs.
7.5"	Black	7500-SB	100	2"	50 lbs.
11"	White	1150-SB	100	3"	50 lbs.
11"	Black	11500-SB	100	3"	50 lbs.

Size	Color	Model #	Pack	Max. Bundle Diameter	Tensile Strength
MOUNTING BASES					
Provides a slide-through base for mounting bundles with standard and outdoor cable ties. Available in indoor and outdoor ultraviolet black. Fits all NSi ties from 4" to 14". Attach to wood studs or flat surfaces with peel-off adhesive back or with wood screws.					
1x1"	White	FTH5A-5R	5	-	-
1x1"	Black	FTH5A-B-5R	5	-	-

Length	Color	Model #	Pack
CABLE TIE TIGHTENING TOOL			
Slide tail of all NSi cable ties into side slot of this tool and pull trigger repeatedly to ratchet bundle tight. Snap-off excess cable tie length with a quick twist.			
6 1/2"	Red	TRT-200	1

Cable Tie Canisters

Three different canisters to match your promotional needs. Each canister has a mixture of cable tie length, color, max bundle diameter, and tensile strength.



Length	Color	Model #	Pack	Max. Bundle Diameter	Tensile Strength
300 PIECE CABLE TIE CANISTER					
Resealable zip-lock bags for easy storage Nylon 6/6, UL recognized Meets UL 94 V-2 flammability classification Ultraviolet ties have additive to resist outdoor sunlight deterioration					
4"	White	CTP-300BW	100	7/8"	18 lbs.
4"	Black		100	7/8"	18 lbs.
8"	White		100	2 1/8"	40 lbs.
500 PIECE CABLE TIE CANISTER					
4"	White	CTP-500W	200	7/8"	18 lbs.
6"	White		100	1 3/8"	40 lbs.
8"	White		200	2 1/8"	40 lbs.
650 PIECE CABLE TIE CANISTER					
4"	White	CTP-650	100	7/8"	18 lbs.
4"	Yellow		50	7/8"	18 lbs.
4"	Red		50	7/8"	18 lbs.
4"	Green		50	7/8"	18 lbs.
4"	Black		50	7/8"	18 lbs.
8"	White		300	2 1/8"	40 lbs.
11"	White		50	3"	50 lbs.

See www.nsiindustries.com for hundreds of additional cable tie categories including: HVAC Ties for Flexible Duct, Air Handling Ties, Push-Mount Ties, Tefzel Ties, In-Line Ties, Hook and Loop Tie Rolls, Stainless Ties in Lengths to 47 inches, Cable Tie Saddle Mounts, Cable Tie Push Mounts, Heavy-Duty Cable Tie, and Installation Tools.






SunSet[™]
TORK® DIGITAL TIMERS



NSI Industries LLC • Huntersville, NC • USA • Phone 800.321.5847 • Fax 800.841.5566 • www.nsiindustries.com

Wire Management

An essential part of residential and commercial wiring installation is routing wires and cables along and through walls, between floors and along exterior surfaces. The goal is to keep them compact, organized for appearance and traceability, and bundled so that walls and ceilings can be safely completed and sealed. NSi offers many types of specific-use staples, nail-on clips, ratcheting clips and clamps, and flexible plastic wrap and conduits. Each package is resealable for storage of unused products.

SWITCHES
SPLIT BOLTS
WIRE MANAGEMENT




CONNECTORS
MECHANICAL LUGS
TESTERS
GROUNDING

TESTERS
GROUNDING
MECHANICAL LUGS


Wire Management

A complete assortment of staples, clamps, wraps, tapes, hole sealers, wire markers, and heat shrink insulators to organize and manage electrical wireways.



Size	Color	Model #	Pack
LOW VOLT CABLE STAPLES			
Single-nail staple with plastic cradle designed to fasten telephone, speaker and other low-volt wires to wood studs, molding and other surfaces. White and Black color for decorative use.			
3/16"	White	BWSP-187-25R	25
3/16"	White	BWSP-187-100R	100
3/16"	Black	BWSP-1870-25R	25
3/16"	Black	BWSP-1870-100R	100
ADJUSTABLE RATCHETING STAPLES			
Unique plastic clamp wraps around wire bundles to organize and route wires neatly under desks, along floors, along walls, etc. Ratcheting action holds wires tightly. Perfect for audio and computers. Peel-off adhesive backs. Black color.			
3/8"	Black	ADJCC-2-6R	6
1/2"	Black	ADJCC-3-4R	4
3/4"	Black	ADJCC-4-2R	2
ONE-HOLE POLY CLAMPS			
All purpose clamps in 5 sizes, wrap around wire bundles to organize and route wires neatly along wooden surfaces. Mounting hole for wood screw fastening. White and black color for decorative use.			
1/4"	White	NC-250N-18R	18
3/8"	White	NC-375N-15R	15
1/2"	White	NC-500N-12R	12
3/4"	White	NC-750N-6R	6
1"	White	NC-1000N-4R	4
1/4"	Black	NC-250B-18R	18
3/8"	Black	NC-375B-15R	15
1/2"	Black	NC-500B-12R	12
3/4"	Black	NC-750B-6R	6
1"	Black	NC-1000B-4R	4
RUBBER HOLE GROMMETS			
For protection of wire from steel cutout edges.			
1/4", 3/8", 1/2", 3/4"	Black	HG-AST	8
FLOOR CABLE DUCT			
2 1/2" wide floor duct for use as safe, temporary enclosure of electrical cords, data cables that may cause a trip hazard.			
2 1/2" x 18' roll	Off White	FD250W	1
2 1/2" x 18' roll	Brown	FD250B	1

NSi plastic staples are packed in Zip-lock bags.



Length	Color	Model #	Pack	Cable type	Pack Type
PLASTIC STAPLES					
With formed plastic cradles for fastening 2 and 3 wire flat and round non-metallic cables to wood studs. Plastic cradle protects cable jackets.					
1/2"	White	PNC-492W-15R	15	14/2, 12/2, 10/2	Reusable Clamshell
3/4"	White	PNC-736W-15R	15	14/3, 12/3, 10/3	Reusable Clamshell
1/2"	White	PNC-492W-50R	50	14/2, 12/2, 10/2	Zip-Lock Bag
3/4"	White	PNC-736W-50R	50	14/3, 12/3, 10/3	Zip-Lock Bag
1/2"	White	PNC-492W-100R	100	14/2, 12/2, 10/2	Zip-Lock Bag
3/4"	White	PNC-736W-100R	100	14/3, 12/3, 10/3	Zip-Lock Bag



Length	Color	Model #	Pack	Cable type	Pack Type
METAL STAPLES					
Standard rust resistant metal staples for fastening 2 and 3 wire flat and round non-metallic cables and other cable and cords to wood studs. Proven nail design resists splitting wood.					
1/2"	Silver	MS50-24R	24	14/2, 12/2, 10/2	Reusable Clamshell
3/4"	Silver	MS50-100R	100	14/2, 12/2, 10/2	Reusable Clamshell
1/2"	Silver	MS75-18R	18	14/3, 12/3, 10/3	Reusable Clamshell
3/4"	Silver	MS75-100R	100	14/3, 12/3, 10/3	Reusable Clamshell
INSULATED METAL STAPLES					
(Dipped heads protecting insulation of cable)					
1/2"	Blue	MSI50-15R	15	14/2, 12/2, 10/2	Reusable Clamshell
1/2"	Blue	MSI50-100R	100	14/2, 12/2, 10/2	Reusable Clamshell




Length	Color	Model #	Pack	Cable type	Pack Type
COAXIAL CABLE STAPLES					
Single-nail staple designed to snap onto 1/4" coaxial cables for quick attachment to wood studs, baseboards, molding and other surfaces. Formed plastic cradle protects insulation. White and black for decorative use.					
1/4"	White	PNC-157W-25R	25	RG-59/RG-6	Reusable Clamshell
1/4"	White	PNC-157W-50R	50	RG-59/RG-6	Reusable Clamshell
1/4"	Black	PNC-157B-25R	25	RG-59/RG-6	Reusable Clamshell
1/4"	Black	PNC-157B-50R	50	RG-59/RG-6	Reusable Clamshell





Length	Color	Model #	Pack
SPIRAL WRAP			
White memory-spring flat plastic strands wind around wire and cable bundles to organize neatly and route according to desired location. Perfect for electronic, audio, computer high and low volt wires. Allows individual wires to be split-off through plastic windings. Not to be used as electrical conduit.			
3/4" wide x 3 1/2' long	White	SRPE-750	1 per bag



Length	Color	Model #	Pack
SPLIT FLEXIBLE TUBING			
Black flexible corrugated plastic tubing is split along its length to allow insertion of wire and cable bundles to organize and conceal cables neatly. Perfect for electronic, audio and automotive cables. Not to be used as electrical conduit.			
3/4" wide x 3 1/2' long	Black	FLX-37510	1 per bag
1/2" wide x 7' long	Black	FLX-5007	1 per bag



Weight	Color	Model #	Pack
DUCT SEAL			
All-purpose moldable compound specifically designed for plugging holes and cracks around electrical wiring applications. Flame proof, non-conductive, non-corrosive, paintable sealant. Stays effective in temperature ranges: -20°F (-29°C) to 350°F (175°C).			
1 pound	Grey	DS184-R	1 pug



Description	Model #	Pack
CIRCUIT BREAKER MARKERS		
Two handy sheets of 45, 1/4" x 1" peel-off adhesive marker strips for identifying many common circuit breaker types. Tough nylon impregnated fabric resists dirt and wear.		
90 Circuit Breaker Marker Strips	WMB-LC	2 Sheets



Model #	Description	Pack
LIQUID ELECTRICAL TAPE		
A liquid coating used to insulate and protect electrical splices and connections. For low voltage application at home, auto/marine.		
LETB-4	Black 4 oz.	1
LETR-4	Red 4 oz.	1
LETW-4	White 4 oz.	1

Packed in Zip-lock bags



SA 242382
UL E245593

Shrink Ratio	Model #	Pack
HEAT SHRINK TUBING		
Versatile 4" thinwall polyolefin heat shrink tubes shrink to 1/2 original diameter when flame or heat is applied. Forms a tight seal around wire connections, cord-ends. Flame-retardant. Effective temperature: -55°C (-67°F) to 135°C (275°F) 600V dielectric strength.		
3/32" to 3/64"	TWHS-093-4-8R	8
1/8" to 1/16"	TWHS-125-4-7R	7
3/16" to 3/32"	TWHS-187-4-8R	8
1/4" to 1/8"	TWHS-250-4-6R	6
3/8" to 3/16"	TWHS-375-4-3R	3
1/2" to 1/4"	TWHS-500-4-3R	3
3/4" to 3/8"	TWHS-750-4-2R	2
1" to 1/2"	TWHS-1000-4-2R	2
Assorted Pack	THK-AST-8R	8



Length	Model #	For Cable	Pack
UNDERGROUND UF CABLE AND BUTT SPLICE KITS			
Heavy-duty mastic-lined polyolefin heat shrink tubes, shrink to 1/2 original diameter when torch or heat gun is applied. Tubing shrinks and mastic melts to form a waterproof, shovel-proof underground seal. Special brass butt splice connectors fit wires from 2 to 14 AWG.			
8" with 4 wire brass butt splice with plastic ferrule	SKDB-R	8-14 AWG 4 Wire UF	1
4" with 2 wire brass butt splice	SKCB-2-R	8-2 AWG wire	1
4" with 2 wire brass butt splice	SKCB-8-R	8-14 AWG wire	1
WRAP-AROUND GEL SPLICE KIT- HIGH VOLTAGE			
Quickly seal and insulate buried electrical connections up to 1000 volts			
3" Length	WAGS-4/0-4	14-4/0 AWG	1
SNAP-AROUND GEL SPLICE KIT- LOW VOLTAGE			
Quickly seal and insulate low voltage cable connections. Set screw terminal block.			
-	ESGTS-2	2-14 AWG	1

UNDERGROUND CABLE BURIAL SPLICING KITS

See www.nsiindustries.com for a complete listing of UL-approved splice kits for underground burial of wires and cables. Included in NSI's offering are: Wrap-Around and Roll-On Gel Kits for high and low-voltage wires, Heavy-Wall mastic-lined heat shrink tubes and end caps in multiple sizes and kits, and our exclusive Polaris-brand direct burial rubber insulated tap connector line.



EASY-WRAP™ Electrical Tape

Flexible, stretchable UL and CSA listed vinyl tapes in black and colors as well as friction and self-bonding tape specifically designed for electrical use. Always use approved wire connectors for joining conductors



Length	Color	Model #	Pack
--------	-------	---------	------

EASY-WRAP™ GENERAL PURPOSE ELECTRICAL TAPES

Flexible 7 mil thick adhesive backed tape, ideal for wrapping electrical conductors. Insulates to 600V. Effective to -7 to 80°C (176°F). Flameproof.

30' x 3/4"	Black	EWG 7030	Sleeve of 10
60' x 3/4"	Black	EWG 7060-LL	Sleeve of 10
60' x 3/4"	Brown	EWG 7060-1	Sleeve of 10
60' x 3/4"	Red	EWG 7060-2	Sleeve of 10
60' x 3/4"	Orange	EWG 7060-3	Sleeve of 10
60' x 3/4"	Yellow	EWG 7060-4	Sleeve of 10
60' x 3/4"	Green	EWG 7060-5	Sleeve of 10
60' x 3/4"	Blue	EWG 7060-6	Sleeve of 10
60' x 3/4"	Purple	EWG 7060-7	Sleeve of 10
60' x 3/4"	White	EWG 7060-9	Sleeve of 10

EASY-WRAP™ PREMIUM ELECTRICAL TAPES - Plastic Pucks

Effective to -18 to 105°C (176°F). Flameproof. 66' rolls, sold in packs of 10

66' x 3/4"	Black	EWG 7066	10 Pucks
66' x 3/4"	Brown	EWG 7066-1	10 Pucks
66' x 3/4"	Red	EWG 7066-2	10 Pucks
66' x 3/4"	Orange	EWG 7066-3	10 Pucks
66' x 3/4"	Yellow	EWG 7066-4	10 Pucks
66' x 3/4"	Green	EWG 7066-5	10 Pucks
66' x 3/4"	Blue	EWG 7066-6	10 Pucks
66' x 3/4"	Purple	EWG 7066-7	10 Pucks
66' x 3/4"	Grey	EWG 7066-8	10 Pucks
66' x 3/4"	White	EWG 7066-9	10 Pucks

Length	Color	Model #	Pack
--------	-------	---------	------

COLORED ELECTRICAL TAPE ASSORTMENT

Multi-purpose 7 mil thick adhesive backed colored tapes. Insulated to 600V. Effective to 80°C (176°F). Flameproof. Perfect for organizing conductors.

1/2" wide x 12' long	Red, White, Blue, Green, Yellow	EWG-ASTCR-5R	5 Rolls
----------------------	---------------------------------	--------------	---------

Length	Color	Model #	Pack
--------	-------	---------	------

EASY-WRAP™ FRICTION TAPE

For use with any electrical connection and splicing.

3/4" wide x 60' long	Black	EWFT 157560	1 Roll
----------------------	-------	-------------	--------

Length	Color	Model #	Pack
--------	-------	---------	------

SELF BONDING FUSION TAPE


Insulates and waterproofs, stretches up to 300% original size. Adhesive, forming permanent bonds, insulating up to 8000V per layer. Resistive to UV, oil and corrosion.

1" wide x 10' long	Black	EWSR 121010	1 roll
--------------------	-------	-------------	--------


WIRE MANAGEMENT


NSi Ratchet Clamps

Unique, feature-packed ratcheting clamps secure cables, hoses, small electronic cords from 1" to 3" bundle diameter tightly for storage and carrying. Carrying handle and pop-up hanging loop included. Re-usable, adjustable, rugged with push-button release



Model #	Bundle Diameter	Color	Pack
SMALL CLAMP			
RCC-1-50	1"	Black	Full color display pack of 50
MEDIUM CLAMP			
RCC-2-34	2"	Black	Full color display pack of 34
LARGE CLAMP			
RCC-3-25	3"	Black	Full color display pack of 25





TORK®

nsi
INDUSTRIES

TORK

Since 1922 TORK has offered a broad compliment of the highest quality heavy duty timers and time switches. In 2008, TORK began to offer a complete and competitive line of indoor and outdoor plug-in, in-wall and stake mounted timers. TORK has spent significant resources on market research to help the consumer make educated and efficient buying decisions when purchasing a timer. By appealing to the shopper's needs (Color / Shape / Imagery / Iconography), TORK uses easy-to-spot packaging colors to guide the consumer to both indoor and outdoor applications.


RESEARCH

HOW WE SEE, IS HOW WE SHOP

The order in which the human eye sees

1. Color
2. Shape
3. Imagery
4. Words

Color	Shape	Imagery	Words
-------	-------	---------	-------



NEW!!
Heavy Duty
Astronomic
Push-Pin
24-Hour

RESULTS


OUTDOOR - INDOOR

The differences between the outdoor and the indoor timer designs are distinguished by Color, Typography, Imagery, and Iconography.


Tork's new packaging combines these ideas into one, simple package. Allowing the customer to make an easy decision when faced with multiple choices at the retailer.

TORK. It's about time.

Color	Typography	Imagery	Iconography
-------	------------	---------	-------------



OUTDOOR



INDOOR



TORK PACKAGING CONCEPT

RESEARCH SHOWS:

TORK® is the trusted timer of professionals since 1922.

TORK® is the backbone for the lighting of the empire state building, among other landmarks.

TORK® product exceeds all safety standards and personal timing needs.

TORK®. It's about time.



PLANOGRAM



indoor timers

SunSet



outdoor timers



Indoor Mechanical Plug-Ins

- Automatically turn ON/OFF items in the home.
- Give the home a "lived in" look while away.
- Control lamps, radios, televisions, appliances.
- Save energy and provide security.



Catalog NO.	UPC	Ratings 60Hz	Outlets (▶)	Type of Plug	Description	Variable Timing Segments
403B	16085		1	Polarized 2 Conductor	Easy-Set Basic Timer	30 minutes
403B2	16088	125VAC 15A 1875W Resistive, 125VAC 500W Tungsten, 125VAC 1/3 HP	1	Polarized 2 Conductor	Easy-Set Basic Timer (2 pack)	30 minutes
402B	16091		1	Grounded 3 Conductor	Air Conditioner Timer	30 minutes
422A	16019	125VAC 15A 1875W Resistive, 125VAC, 500W Tungsten, 125VAC TV-4	1	Grounded 3 Conductor	Aquarium and Grow Light Timer	30 minutes
405B	16094	125VAC 15A 1875W Resistive, 125VAC 500W Tungsten, 125VAC 500VA Electronic Ballast, 125VAC TV-4	2	Grounded 3 Conductor	Easy-Set Heavy Duty Timer	30 minutes
459A	16035	125VAC 15A 1875W Resistive, 125VAC 10A 1250W Tungsten, 125VAC 1/3 HP	8	Grounded 3 Conductor	Home Office 8 Outlet Timer	15 minutes

NOTE: "▲" = Indicates outlet location.



Outdoor Mechanical Plug-Ins

- Automatically turn ON/OFF outdoor lighting.
- Save energy. Don't run lights all night.
- Automatic ON at dusk with light activated timer



Catalog NO.	UPC	Ratings 60Hz	Outlets (▷)	Type of Plug	Description	Variable Timing Segments
602B	16106	125VAC 15A Resistive, 125VAC 500W Tungsten, 125VAC 500VA Electronic Ballast, 125VAC 1/3 HP	2	Grounded 3 Conductor	Outdoor Lighting Timer	30 minutes
652B	16108	125VAC 15A Resistive, 125VAC 1000W Tungsten, 125VAC 500VA Electronic Ballast, 125VAC 1/3 HP TV-5	2	Grounded 3 Conductor	Light-Activated Holiday Decor Timer	2, 4, 6, 8 Hours

NOTE: "▲" = Indicates outlet location.



Indoor Digital Plug-Ins

- Automatically turn ON/OFF items in the home.
- Control lamps, radios, televisions, appliances.
- Give the home a "lived in" look while away.
- Save energy and provide security.



Catalog NO.	UPC	Ratings	Outlets (▶)	Type of Plug	Description	Variable Timing Segments
460E	16097	125VAC 15A 1875W Resistive, 125VAC 1000W Tungsten, 125VAC 500VA Electronic Ballast, 1/3 HP	1	Polarized 2 Conductor	Easy-Set Digital Basic Timer	24/7
454E	16100	125VAC 15A 1875W Resistive, 125VAC 1000W Tungsten, 125VAC 500VA Electronic Ballast, 1/3 HP	1	Grounded 3 Conductor	Digital Lamp Timer	24/7
455E	16103	120VAC 15A 1800W Resistive, 120VAC 960W Tungsten, 120VAC 500VA Electronic Ballast, 1/2 HP	2	Grounded 3 Conductor	Air Conditioner Digital Timer	24/7
457Z	16016	125VAC 15A 1875W Resistive, 125VAC 1000W Tungsten	2	Grounded 3 Conductor	SunSet Security Timer	24/7

NOTE: "▲" = Indicates outlet location.



INDOOR DIGITAL PLUG-INS

Outdoor Digital Plug-Ins

- Automatically turn ON/OFF outdoor lighting.
- Save energy. Don't run lights all night.
- Automatic ON at dusk with light activated timer



Catalog NO.	UPC	Ratings	Outlets (▶)	Type of Plug	Description	Variable Timing Segments
642E	16110	125VAC 15A Resistive, 125VAC 1000W Tungsten, 125VAC 500VA Electronic Ballast, 125VAC 1/3 HP	2	Grounded 3 Conductor	Outdoor Lighting Timer	7 day
654E	16113	125VAC 15A Resistive, 125VAC 1000W Tungsten, 125VAC 500VA Electronic Ballast, 125VAC 1/3 HP TV-5	2	Grounded 3 Conductor	Light-Activated Home Safe Timer	1 to 9 Hours

NOTE: "▲" = Indicates outlet location.



Outdoor Stake Timers

- FAST and EASY programming with ZIP-SET™ One-Step™ Set up.
- Just enter your area code.
- ZIP-SET™ turns lights ON at sunset & OFF at preset time.
- Ideal for outdoor living applications such as lighting, pools & spas.



Catalog NO.	UPC	Ratings	Outlets (▶)	Type of Plug	Description	Variable Timing Segments
SA215	16540	125VAC 60Hz 15A 1875W Resistive, 10A 1250W Tungsten, ½HP	6	Grounded 3 Conductor	Holiday Decor Stake Timer	30 Minute Intervals
SA220	16543	120VAC 60Hz 15A 1800W Resistive, 15A 1800W Inductive, 5A 600W Tungsten, 5A 600W Incandescent, ¼HP	7	Grounded 3 Conductor	Zip-Set Landscape Stake Timer	24/7

NOTE: "▲" = Indicates outlet location.



OUTDOOR STAKE TIMERS



SA215




SA220

In-Wall Mechanical Timers (A Series)



- No electricity needed to operate.
- Turns OFF at the end of timed cycle.
- 2-in-1 SPDT contacts include SPST.



Catalog NO.	UPC	Ratings	Color	Contacts	Description	Variable Timing Segments
A530M	15014	125VAC 20A Resistive/ Inductive, 250VAC 10A Resistive/ Inductive, 277VAC 10A Resistive/ Inductive, 125VAC 7A Tungsten, 125VAC 1HP, 250VAC 2HP	Ivory	SPST/SPDT	Springwound Interval Time Switch	0-30 Minutes
A560M	15015		Ivory	SPST/SPDT	Springwound Interval Time Switch	0-60 Minutes
A560MW	15115		White	SPST/SPDT	Springwound Interval Time Switch	0-60 Minutes

NOTE: Wall plate not included



A530M

A560M

A560MW

IN-WALL MECHANICAL TIMERS

In-Wall Mechanical Timers (C Series)

- No electricity needed to operate.
- Switch contacts are made when knob is rotated at the end of timed cycle the load is turned OFF.
- 2-in-1 SPDT contacts include SPST.



Catalog NO.	UPC	Ratings	Color	Contacts	Description	Variable Timing Segments
C502H	15507	125VAC 20A Resistive/ Inductive, 250VAC 10A Resistive/ Inductive, 277VAC 10A Resistive/ Inductive,	Metal	SPST/SPDT	Springwound Interval Time Switch	0-2 Hours
C515M	15501	125VAC 7A Tungsten, 125VAC 1HP, 250VAC 2HP	Metal	SPST/SPDT	Springwound Interval Time Switch	0-15 Minutes



C502H



C515M

In-Wall Digital Timers

- Different schedule for each day of the week with 7 ON/OFF settings.
- SunSet for Dusk to Dawn timing
- SS700Z no neutral required.



Catalog NO.	UPC	Ratings	Contacts	Description	Variable Timing Segments
SS720A	14017	120VAC 15A 1800W General Purpose, 120VAC 15A 1800W Resistive, 120VAC 15A Tungsten, 120VAC 1HP, 120VAC 500VA Electronic Ballast	Single Pole	Digital Interior Lighting Timer	24/7
SS700Z	14019	120/277VAC 16A 1920/4432W Resistive, 120/277VAC 10A Ballast, 120/277VAC 10A LED Driver, 120VAC 8A 960W Tungsten, 120VAC 1/2HP	Single Pole/3-Way	Digital Sun-Set Exterior Lighting Timer	24/7
SS720Z	14032	120VAC 15A 1800W General Purpose, 120VAC 15A 1800W Resistive, 120VAC 960W Tungsten, 120VAC 1/2HP Motor TV-8, 120VAC 500VA Electronic Ballast	Single Pole	Digital Sun-Set Exterior Lighting Timer	24/7



IN-WALL DIGITAL TIMERS

In-Wall Countdown Timers

- Automatically turn ON/OFF outdoor lighting.
- Save energy. Don't run lights all night.
- Automatic ON at dusk with light activated timer



Catalog NO.	UPC	Ratings	Contacts	Description	Variable Timing Segments
D1060MW	14026	120VAC 60Hz 15A General Purpose, 120VAC 1000W Tungsten, 120VAC 1000W Ballast, 120VAC 1/4HP	Single Pole	Digital Countdown Timer	0-60 Minutes



1101B SERIES

24 Hour Time Switch



Catalog NO.	UPC	Input Supply 60Hz	Contacts	Description	Variable Timing Segments
1101B	10064	120VAC	SPST	24 Hour Time Switch	24 Hour
1102B	10065	208-277VAC	SPST	24 Hour Time Switch	24 Hour
1103B	10066	120VAC	DPST	24 Hour Time Switch	24 Hour
1104B	10067	208-277VAC	DPST	24 Hour Time Switch	24 Hour
1104B-0	10075	208-277VAC	DPST	24 Hour Time Switch Outdoor Enclosure	24 Hour

TYPE	VOLTAGE 60 Hz	RATING
General Purpose	120-277VAC	40A
Resistive	120-277VAC	40A
Tungsten	120VAC	40A
Ballast	120-277VAC	20A
LED Driver	120-277VAC	20A
Pilot Duty	120VAC	1000VA
	240VAC	2000VA
Motor	120VAC	2HP
	240VAC	5HP
277VAC Single Phase		

ELECTROMECHANICAL TIME SWITCHES

WH2B

Water Heater Time Switch



Catalog NO.	UPC	Ratings	Contacts	Description	Variable Timing Segments
WH2B	70044	250VAC 40A 10,000W General Purpose, 250VAC 40A 10000W Resistive	DPST	Water Heater Time Switch	24 Hour

FEATURES:

- Save energy every day. Turn off when not needed
- Minimum ON time 20 minutes, minimum OFF time 75 minutes
- ON/OFF Indicator
- Easy manual override without opening door
- Easy-read day night dial face
- Removable door for easy installation
- Lockable hasp for security

APPLICATIONS:

- Electric Water Heaters
- Control pumps-motors-fans
- Control heating and air conditioning

SPECIFICATIONS:

- Motor Input: 208-250V 60Hz
- Contact Ratings: 40A 250VAC, 10,000 Watts 250VAC
- Screw Terminals accept #8 - #14 AWG
- NEMA 1 Indoor metal enclosure, lockable
- DPST Contacts



TU40

Universal Multi-Voltage Electromechanical Time Switch



Catalog NO.	UPC	Input Supply 60Hz	Contacts	Description	Variable Timing Segments
TU40	24000	120/208-240/277VAC	DPDT	Mechanical Universal Multi-Voltage Time Switch	24 Hour

TYPE	VOLTAGE 60 Hz	RATING	
		NO	NC
Resistive	120-277VAC	40A	30A
	28VDC	20A	-
Inductive	120-277VAC	30A	15A
Ballast	120VAC	30A	10A
	277VAC	20A	10A
Tungsten	120VAC	15A	-
Pilot Duty	120VAC	720 VA	-
	125VAC	-	290VA
	240VAC	720 VA	360 VA
Motor	120VAC	1 HP 30 FLA 90 LRA	1/4 HP 12 FLA 30 LRA
	240VAC	2 HP 20 FLA 60 LRA	-
	250VAC		1/2 HP 12 FLA 33 LRA

FEATURES:

- Automatic Input Voltage Detection
- Quick and easy install
- 24 hour real time clock face
- DPDT, DPST, SPDT, SPST
- Snap fit enclosure
- Captive trippers
- Load On LED indicator
- Power On LED indicator
- ON/OFF/Auto Switch

APPLICATIONS:

- Control pumps-motors-fans
- Control water heaters
- Control signs and lighting
- Control heating and air conditioning



MECHANICAL & DIGITAL TIME SWITCH

DTU40

Universal Multi-Voltage Digital Time Switch



Catalog NO.	UPC	Input Supply 60Hz	Contacts	Description	Variable Timing Segments
DTU40	24004	120/208-240/277VAC	DPDT	Digital Universal Multi-Voltage Time Switch	7 Day

TYPE	VOLTAGE 50/60 Hz	RATING	
		NO	NC
Resistive	120-277VAC	40A	30A
	28VDC	20A	-
Inductive	120-277VAC	30A	15A
Ballast	120VAC	30A	10A
	277VAC	20A	10A
Tungsten	120VAC	15A	-
Pilot Duty	120VAC	720 VA	-
	125VAC	-	290VA
	240VAC	720 VA	360 VA
Motor	120VAC	1 HP 30 FLA 90 LRA	1/4 HP 12 FLA 30 LRA
	240VAC	2 HP 20 FLA 60 LRA	-
	250VAC		1/2 HP 12 FLA 33 LRA

FEATURES:

- Automatic Input Voltage Detection
- Quick and easy install
- 7 Day digital timer
- DPDT, DPST, SPDT, SPST
- Snap fit enclosure
- Load On LED indicator
- Power On LED indicator
- Manual daylight savings
- Manual override button
- Battery back-up

APPLICATIONS:

- Control pumps-motors-fans
- Control water heaters
- Control signs and lighting
- Control heating and air conditioning



NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
EASY-TWIST™ Standard Wire Connectors						
WC-G-14R	Gray Standard Wire Connector: 22-14 AWG Max: 1 #14 w/1 #20 Min: 2 #22 300 volts max.	Clamshell	14	662381400000	10	50662381416884
WC-G-25R		Zip-Bag	25	662381400222	25	50662381416204
WC-G-B		Bulk-Bag	1000	662381354921	26	662381367013
WC-G-C		Box	100	662381361479	10	50662381416846
WC-G-SJ		Jar	300	662381140173	50	66238141727
WC-B-14R	Blue Standard Wire Connector: 22-14 AWG Max: 3 #16 Min: 2 #22 300 volts max.	Clamshell	14	662381400017	10	50662381407226
WC-B-25R		Zip-Bag	25	662381400239	25	50662381407486
WC-B-B		Bulk-Bag	1000	662381353061	18	662381367006
WC-B-C		Box	100	662381361455	10	50662381407745
WC-B-SJ		Jar	300	662381142399	50	66238141726
WC-O-12R	Orange Standard Wire Connector: 22-14 AWG Max: 4 #16 w/1 #20 Min: 1 #18 w/1 #20 600 volts max.	Clamshell	12	662381400024	10	50662381407240
WC-O-25R		Zip-Bag	25	662381400246	25	50662381407509
WC-O-B		Bulk-Bag	500	662381361868	16	662381367020
WC-O-C		Box	100	662381361516	10	50662381407769
WC-O-CJ		Jar	100	662381142306	50	66238141728
WC-Y-9R	Yellow Standard Wire Connector: 22-10 AWG Max: 1 #10 w/2#14 w/1 #16 Min: 3 #20 600 volts max.	Clamshell	9	662381400031	10	50662381407264
WC-Y-25R		Zip-Bag	25	662381400253	25	50662381407523
WC-Y-B		Bulk-Bag	500	662381361882	12	662381367044
WC-Y-C		Box	100	662381361578	10	50662381407783
WC-Y-CJ		Jar	100	662381142313	50	66238141730
WC-R-6R	Red Standard Wire Connector: 22-10 AWG Max: 3 #10 Min: 3 #18 600 volts max.	Clamshell	6	662381400048	10	50662381407288
WC-R-25R		Zip-Bag	25	662381400260	25	50662381407547
WC-R-B		Bulk-Bag	500	662381361875	8	662381367037
WC-R-C		Box	100	662381361547	10	50662381407806
WC-R-SJ		Jar	100	662381142429	20	66238141729
EASY-TWIST™ Standard Wire Connectors Assortment Packs						
WC-A-9R	WC-G, WC-O, WC-Y, WC-R	Clamshell	9	662381400055	10	66238141727
WC-A-25R	WC-G, WC-B, WC-O, WC-Y, WC-R	Zip-Bag	25	662381400277	25	50662381407226
WC-AYR-160R	WC-R, WC-Y	Jar	160	662381400697	4	50662381407486
EASY-TWIST™ Wing Wire Connectors						
WWC-Y-6R	Yellow Wing Wire Connectors: 22-14 AWG Max: 3 #12 Min: 2 #18 600 volts/300 volt**	Clamshell	6	662381400062	10	50662381407325
WWC-Y-25R		Zip-Bag	25	662381400284	25	50662381407585
WWC-Y-B		Bulk-Bag	500	662381361967	12	662381367105
WWC-Y-C		Box	100	662381361806	10	50662381407820
WWC-Y-CJ		Jar	100	662381142320	50	66238141736
WWC-R-6R	Red Wing Wire Connectors: 18-8 AWG Max: 5 #12 Min: 3 #16 600 volts/300 volt**	Clamshell	6	662381400079	10	50662381407349
WWC-R-25R		Zip-Bag	25	662381400291	25	50662381407608
WWC-R-B		Bulk-Bag	500	662381361943	7	662381367082
WWC-R-C		Box	100	662381361745	10	50662381407868
WWC-R-SJ		Jar	100	662381142450	20	66238141734
WWC-T-6R	Tan Universal Wing Wire Connectors: 22-8 AWG Max: 3 #10 Min: 3 #22 600 volts/300 volt	Clamshell	6	662381400116	10	50662381407424
WWC-T-25R		Zip-Bag	25	662381400338	25	50662381407684
WWC-T-B		Bulk-Bag	500	662381361950	10	662381367099
WWC-T-C		Box	100	662381361776	10	50662381407844
WWC-T-CJ		Jar	100	662381142337	50	66238141735
WWC-G-6R	Gray Wing Wire Connectors: 18-8 AWG Max: 3 #10 Min: 3 #14 w/1 #18 600 volts max**	Clamshell	6	662381400123	10	50662381407448
WWC-G-25R		Zip-Bag	25	662381400345	25	50662381407707
WWC-G-B		Bulk-Bag	250	662381361905	11	662381367068
WWC-G-C		Box	50	662381361639	10	50662381407882
WWC-G-SJ		Jar	50	662381142467	20	66238141733
WWC-B-2R	Blue Wing Wire Connectors: 14-6 AWG Max: 1 #8 w/3 #10 Min: 2 #10 w/1 #12 600 volts max**	Clamshell	2	662381400086	10	50662381407363
WWC-B-10R		Zip-Bag	10	662381400307	20	50662381407622
WWC-B-B		Bulk-Bag	100	662381361899	14	662381367051
WWC-B-C		Box	50	662381361608	10	50662381407905
WWC-B-SJ		Jar	50	662381142474	20	66238141731
EASY-TWIST™ Wing Wire Connectors Assortment Packs						
WWC-A-5R	WWC-Y, WWC-R, WWC-G	Clamshell	5	662381400093	10	50662381407387
WWC-A-25R	WWC-Y, WWC-R, WWC-T, WWC-B	Zip-Bag	25	662381400314	25	50662381407646
WWC-AYR-160R	WWC-R, WWC-Y	Jar	160	662381400703	4	50662381408186

PRODUCT SET-UP INFORMATION

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
2.95	4.65	0.07	16.93	3.35	4.92	0.16	0.73	
3.74	7.24	0.11	7.01	3.94	14.17	0.23	1.13	
7.87	-	0.45	14.56	9.64	12.59	1.00	12.23	
2.56	2.17	0.15	13.58	3.74	4.72	0.14	1.46	
2.64	5.59	0.19	16.14	10.98	16.14	1.70	10.00	
2.95	4.65	0.08	16.93	3.35	4.92	0.16	0.81	
3.74	7.24	0.15	7.01	3.94	14.17	0.23	1.46	
7.87	-	0.70	14.56	9.64	12.59	1.00	13.10	
2.56	2.17	0.20	13.58	3.74	4.72	0.14	1.98	
2.64	5.59	0.25	16.14	10.98	16.14	1.70	12.98	
2.95	4.65	0.09	16.93	3.35	4.92	0.16	0.94	
3.74	7.24	0.23	7.01	3.94	14.17	0.23	2.33	
7.87	-	0.67	14.56	9.64	12.59	1.00	11.10	
2.95	2.76	0.37	15.55	4.33	5.91	0.23	3.69	
2.64	5.59	0.18	16.14	10.98	16.14	1.70	9.55	
2.95	4.65	0.10	16.93	3.35	4.92	0.16	0.96	
3.74	7.24	0.31	7.01	3.94	14.17	0.23	3.09	
9.84	-	0.95	14.56	9.64	12.59	1.00	11.80	
2.95	2.76	0.49	15.55	4.33	5.91	0.23	4.90	
2.64	5.59	0.23	16.14	10.98	16.14	1.70	12.10	
2.95	4.65	0.09	16.93	3.35	4.92	0.16	0.94	
3.75	8.58	0.41	7.01	3.94	14.17	0.23	4.09	
10.63	-	1.43	14.56	9.64	12.59	1.00	11.80	
3.54	3.15	0.67	18.50	4.92	6.38	0.34	6.65	
3.74	5.90	0.44	16.14	10.98	16.14	1.70	9.40	
2.95	4.65	0.09	16.93	3.35	4.92	0.16	0.91	
3.75	8.58	0.26	7.01	3.94	14.17	0.23	2.65	
3.74	5.91	0.40	15.28	3.74	6.10	0.20	4.04	
2.95	4.65	0.08	16.93	3.35	4.92	0.16	0.83	
3.74	7.24	0.30	7.01	3.94	14.17	0.23	2.99	
9.84	-	0.91	14.56	9.64	12.59	1.00	11.40	
2.95	2.76	0.47	15.55	4.33	5.91	0.23	4.74	
2.64	5.59	0.23	16.14	10.98	16.14	1.70	11.90	
2.95	4.65	0.10	16.93	3.35	4.92	0.16	1.03	
3.74	7.24	0.41	7.01	3.94	14.17	0.23	4.10	
10.63	-	1.68	14.56	9.64	12.59	1.00	12.20	
3.54	3.15	0.82	18.50	4.92	6.38	0.34	8.22	
3.74	5.90	0.41	16.14	10.98	16.14	1.70	8.91	
2.95	4.65	0.08	16.93	3.35	4.92	0.16	0.84	
3.74	7.24	0.30	7.01	3.94	14.17	0.23	3.04	
9.84	-	0.98	14.56	9.64	12.59	1.00	10.20	
3.35	2.76	0.49	17.52	4.92	5.91	0.29	4.94	
2.64	5.59	0.23	16.14	10.98	16.14	1.70	12.22	
2.95	4.65	0.12	16.93	3.35	4.92	0.16	1.25	
3.75	8.58	0.45	7.01	3.94	14.17	0.23	4.49	
7.87	-	1.23	14.56	9.64	12.59	1.00	14.00	
3.35	2.76	0.63	17.52	4.92	5.91	0.29	6.34	
3.74	5.90	0.34	16.14	10.98	16.14	1.70	7.40	
2.95	4.65	0.09	16.93	3.35	4.92	0.16	0.92	
3.75	8.58	0.37	7.01	3.94	14.17	0.23	3.69	
7.87	-	1.23	14.56	9.64	12.59	1.00	14.00	
3.54	3.54	0.90	18.50	5.31	7.48	0.43	9.04	
3.74	5.90	0.46	16.14	10.98	16.14	1.70	9.81	
2.95	4.65	0.09	16.93	3.35	4.92	0.16	0.93	
3.75	8.58	0.43	7.01	3.94	14.17	0.23	4.28	
3.74	5.91	0.45	15.28	3.74	6.10	0.20	4.49	

NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
EASY-TWIST™ Green Grounding Wire Connectors						
WWC-GR-6R		Clamshell	6	662381400109	10	50662381407400
WWC-GR-25R	Green Grounding	Zip-Bag	25	662381400321	25	50662381407660
WWC-GR-B	Wing Connector	Bulk-Bag	500	662381361912	9	662381367075
WWC-GR-C	Max: 5 #12 min: 2 #14	Box	100	662381361653	10	50662381407929
WWC-GR-SJ		Jar	100	662381142504	20	66238141732
Push-In Solid and Stranded Wire Connectors						
PIWC-2-10R	Yellow Push-In Connector 2 PORT 22-12 AWG	Clam	10	662381400352	10	662381400352
PIWC-2		Box	100	662381159663	45	662381159663
PIWC-3-10R	Orange Push-In Connector 3 PORT 22-12 AWG	Clam	10	662381400369	10	662381400369
PIWC-3		Box	100	662381159670	45	662381159670
PIWC-4-10R	Clear Push-In Connector 4 PORT 22-12 AWG	Clam	10	662381400376	10	662381400376
PIWC-4		Box	100	662381159687	45	662381159687
PIWC-8-5R	Black Push-In Connector 8 PORT 22-12 AWG	Clam	5	662381400383	10	662381400383
PIWC-8		Box	50	662381159700	45	662381159700
Steel Crimp Sleeve Connectors-Brass Coated						
SB1810S-12R	18-12 AWG	Clam	12	662381402424	10	50662381410004
SB1810S		Clam	100	662381402448	10	50662381410042
SB1408S-8R	14-8 AWG	Clam	8	662381402431	10	50662381410028
SB1408S		Clam	100	662381402455	10	50662381410066
Nylon Pigtail Connectors						
C22-N-10R	22-16 AWG	Clam	10	662381402301	10	50662381409947
C16-N-10R	16-14 AWG	Clam	10	662381402318	10	50662381409961
C12-N-8R	12-10 AWG	Clam	8	662381402325	10	50662381409985
Grounding Accessories						
GSC-12R	Grounding Screws	Clam	12	662381402844	10	50662381410301
GSC		Clam	100	662381402882	10	50662381410325
PG12C-2R	Grounding Pigtails	Clam	2	662381402868	10	50662381410363
PG12SC		Clam	50	662381362803	20	662381417404
GGC-1000-8R	Grounding Clips	Clam	8	662381402875	10	50662381410349
GZ-1R	Ground Clamp for 1/2" - 1" Pipe	Clam	1	662381402899	10	50662381413982
GRC-50R	Acorn Clamp for 1/2" Pipe	Clam	1	662381402905	10	50662381414002
GRC-58R	Acorn Clamp for 5/8" Pipe	Clam	1	662381402912	10	50662381414026
Copper Split Bolts						
N-8R	16-8 AWG Stranded or Solid	Clam	2	662381407016	5	50662381413203
N-6R	10-6 AWG Stranded or Solid	Clam	2	662381406996	5	50662381413166
N-4R	8-4 AWG Solid	Clam	2	662381407160	5	50662381413647
N-2R	6-2 AWG Solid	Clam	2	662381407177	5	50662381413661
N-1/0R	4-0 AWG Stranded or Solid	Clam	2	662381407030	5	50662381413241
N-2/0R	2-00 AWG Stranded or Solid	Clam	1	662381407047	5	50662381413265
N-3/0R	2-000 AWG Stranded or Solid	Clam	1	662381407054	5	50662381413289
Copper Mechanical Lugs						
DE703R	14-10 AWG Stranded	Clam	2	662381406965	5	50662381413708
DE704R	14-6 AWG Stranded	Clam	2	662381406972	5	50662381413722
DE705R	8-2 AWG Stranded	Clam	2	662381406989	5	50662381413746
DE706R	6-0 AWG Stranded	Clam	2	662381407115	5	50662381413401
Aluminum Split Bolts						
APSO2R	8-2 AWG Stranded	Clam	1	662381407061	5	50662381413302
APS11R	8-0 AWG Solid or Stranded	Clam	1	662381407078	5	50662381413326
APS21R	2-00 AWG Stranded or Solid	Clam	1	662381407085	5	50662381413340
APS41R	6-0000 AWG Stranded	Clam	1	662381407092	5	50662381413364
Aluminum Splicer/Reducers						
2-SRR	14-2 AWG Stranded	Clam	2	662381407146	5	50662381413463
1/0-SRR	14-0 AWG Stranded	Clam	1	662381407153	5	50662381413487
4/0-SRR	14-0000 AWG Stranded	Clam	1	662381406958	5	50662381413760
Aluminum Mechanical Lugs						
2TR	14-2 AWG Stranded	Clam	2	662381407122	5	50662381413425
2/OTR	14-00 AWG Stranded	Clam	2	662381407184	5	50662381413685
Aluminum Anti-Oxidant Solution						
OX-1-1R	Aluminum Anti-Oxidant 1 oz.	Tube	1	662381406880	10	50662381413128
OX-4	Aluminum Anti-Oxidant 4 oz.	Tube	1	662381055224		662381417384

PRODUCT SET-UP INFORMATION

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
2.95	4.65	0.10	16.93	3.35	4.92	0.16	0.96	
3.75	8.58	0.43	7.01	3.94	14.17	0.23	4.34	
9.84	-	1.42	14.56	9.64	12.59	1.00	13.22	
3.35	2.76	0.70	17.52	4.92	5.91	0.29	7.00	
3.74	5.90	0.41	16.14	10.98	16.14	1.70	8.90	
2.95	4.65	0.19	16.93	3.35	4.92	0.16	6.30	
2.95	2.76	0.29	14.56	9.64	12.59	1.00	13.50	
2.95	4.65	0.19	16.93	3.35	4.92	0.16	7.38	
2.95	2.76	0.39	14.56	9.64	12.59	1.00	17.80	
2.95	4.65	0.19	16.93	3.35	4.92	0.16	8.62	
2.95	2.76	0.37	14.56	9.64	12.59	1.00	17.00	
2.95	4.65	0.19	16.93	3.35	4.92	0.16	13.44	
2.95	2.76	0.37	14.56	9.64	12.59	1.00	17.20	
1.77	4.13	0.04	6.46	2.05	4.65	0.04	0.36	
2.95	4.61	0.20	13.98	3.23	5.00	0.13	2.01	
1.77	4.13	0.05	6.46	2.05	4.65	0.04	0.49	
2.87	4.61	0.25	13.98	3.23	5.00	0.13	2.51	
1.77	4.13	0.04	9.21	2.05	4.65	0.05	0.37	
1.77	4.13	0.04	9.21	2.05	4.65	0.05	0.38	
1.77	4.13	0.05	9.21	2.05	4.65	0.05	0.48	
1.77	4.13	0.08	8.07	3.15	4.88	0.86	0.80	
2.94	4.63	0.27	8.07	3.15	4.88	0.86	2.73	
2.94	4.63	0.07	8.07	3.15	4.88	0.86	0.92	
3.50	12.25	1.280	1.25	-	-	-	-	
1.77	4.13	0.04	8.07	3.15	4.88	0.86	0.49	
2.94	4.63	0.14	8.07	3.15	4.88	0.86	0.95	
2.94	4.63	0.09	8.07	3.15	4.88	0.86	0.95	
2.94	4.63	0.10	8.07	3.15	4.88	0.86	0.95	
2.94	4.63	0.08	8.07	3.15	4.88	0.86	0.54	
2.94	4.63	0.13	8.07	3.15	4.88	0.86	0.76	
2.94	4.63	0.16	8.07	3.15	4.88	0.86	0.90	
2.94	4.63	0.23	8.07	3.15	4.88	0.86	1.20	
2.94	4.63	0.18	8.07	3.15	4.88	0.86	1.02	
2.94	4.63	0.21	8.07	3.15	4.88	0.86	1.18	
2.94	4.63	0.32	8.07	3.15	4.88	0.86	1.73	
2.94	4.63	0.06	8.07	3.15	4.88	0.86	0.36	
2.94	4.63	0.07	8.07	3.15	4.88	0.86	0.40	
2.94	4.63	0.12	8.07	3.15	4.88	0.86	0.68	
2.94	4.63	0.24	8.07	3.15	4.88	0.86	1.30	
2.94	4.63	0.086	8.07	3.15	4.88	0.86	0.54	
2.94	4.63	0.10	8.07	3.15	4.88	0.86	0.62	
2.94	4.63	0.13	8.07	3.15	4.88	0.86	0.79	
2.94	4.63	0.29	8.07	3.15	4.88	0.86	1.57	
2.94	4.63	0.09	8.07	3.15	4.88	0.86	0.57	
2.94	4.63	0.07	8.07	3.15	4.88	0.86	0.47	
2.94	4.63	0.16	8.07	3.15	4.88	0.86	0.90	
2.94	4.63	0.06	8.07	3.15	4.88	0.86	0.41	
2.94	4.63	0.08	8.07	3.15	4.88	0.86	0.54	
2.94	4.63	0.06	8.07	3.15	4.88	0.86	0.60	
1.60	6.25	0.30	6.25	5.25	6.50	0.86	3.88	

NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
MINITERM™ Ring Terminals						
R22-6V-10R	22-18 AWG / 4-6 Stud	Clam	10	662381400826	10	50662381408247
R22-8V-10R	22-18 AWG / 8-10 Stud	Clam	10	662381400833	10	50662381408261
R22-6V-22R	22-18 AWG / 4-6 Stud	Clam	22	662381400901	10	50662381408407
R22-8V-22R	22-18 AWG / 8-10 Stud	Clam	22	662381400918	10	50662381408421
R16-6V-10R	16-14 AWG / 4-6 Stud	Clam	10	662381400840	10	50662381408285
R16-8V-10R	16-14 AWG / 8-10 Stud	Clam	10	662381400857	10	50662381408308
R16-14V-7R	16-14 AWG / 12-1/4" Stud	Clam	7	662381400864	10	50662381408322
R16-6V-22R	16-14 AWG / 4-6 Stud	Clam	22	662381400925	10	50662381408445
R16-8V-22R	16-14 AWG / 8-10 Stud	Clam	22	662381400932	10	50662381408469
R16-14V-17R	16-14 AWG / 12-1/4" Stud	Clam	17	662381400949	10	50662381408483
R16-6V-100R	16-14 AWG / 4-6 Stud	Clam	100	662381400987	10	50662381408568
R16-8V-100R	16-14 AWG / 8-10 Stud	Clam	100	662381400994	10	50662381408582
R16-14V-100R	16-14 AWG / 12-1/4" Stud	Clam	100	662381401007	10	50662381408605
R12-8V-8R	12-10 AWG / 8-10 Stud	Clam	8	662381400871	10	50662381408346
R12-14V-7R	12-10 AWG / 12-1/4" Stud	Clam	7	662381400888	10	50662381408360
R12-38V-7R	12-10 AWG / 1/4-3/8" Stud	Clam	7	662381400895	10	50662381408384
R12-8V-14R	12-10 AWG / 8-10 Stud	Clam	14	662381400956	10	50662381408506
R12-14V-14R	12-10 AWG / 1/4-3/8" Stud	Clam	14	662381400963	10	50662381408520
R12-38V-13R	12-10 AWG / 1/4-3/8" Stud	Clam	13	662381400970	10	50662381408544
R12-8V-50R	12-10 AWG / 8-10 Stud	Clam	50	662381401014	10	50662381408629
R12-14V-50R	12-10 AWG / 12-1/4" Stud	Clam	50	662381401021	10	50662381408643
MINITERM™ Spade Terminals						
S22-4V-10R	22-18 AWG / 4-6 Stud	Clam	10	662381401120	10	50662381408667
S22-8V-7R	22-18 AWG / 8-10 Stud	Clam	7	662381401137	10	50662381408681
S22-4V-20R	22-18 AWG / 4-6 Stud	Clam	20	662381401175	10	50662381408766
S22-8V-20R	22-18 AWG / 8-10 Stud	Clam	20	662381401182	10	50662381408780
S22-4V-100R	22-18 AWG / 4-6 Stud	Clam	100	662381401212	10	50662381408841
S22-8V-100R	22-18 AWG / 8-10 Stud	Clam	100	662381401229	10	50662381408865
S16-6V-10R	16-14 AWG / 4-6 Stud	Clam	10	662381401144	10	50662381408704
S16-8V-10R	16-14 AWG / 8-10 Stud	Clam	10	662381401151	10	50662381408728
S16-6V-20R	16-14 AWG / 4-6 Stud	Clam	20	662381401199	10	50662381408803
S16-8V-20R	16-14 AWG / 8-10 Stud	Clam	20	662381401205	10	50662381408827
S16-6V-100R	16-14 AWG / 4-6 Stud	Clam	100	662381401236	10	50662381408889
S16-8V-100R	16-14 AWG / 8-10 Stud	Clam	100	662381401243	10	50662381408902
S12-8V-8R	12-10 AWG / 8-10 Stud	Clam	8	662381401168	10	50662381408742
S12-8V-50R	12-10 AWG / 8-10 Stud	Clam	50	662381401250	10	50662381408926
MINITERM™ Female/Male Disconnect Terminals (Barrel Insulated)						
F22-250-3V-10R	Female 22-18 AWG 1/4" Tab	Clam	10	662381401533	10	50662381409121
F22-250-3V-21R	Female 22-18 AWG 1/4" Tab	Clam	21	662381401595	10	50662381409244
F16-187-2V-10R	Female 16-14 AWG 1/4" Tab	Clam	10	662381401557	10	50662381409169
F16-187-2V-20R	Female 16-14 AWG 1/4" Tab	Clam	20	662381401618	10	50662381409282
F12-250-3V-8R	Female 12-10 AWG 1/4" Tab	Clam	8	662381401571	10	50662381409206
F12-250-3V-16R	Female 12-10 AWG 1/4" Tab	Clam	16	662381401632	10	50662381409329
M22-250-3V-10R	Male 22-18 AWG 1/4" Tab	Clam	10	662381401540	10	50662381409145
M22-250-3V-18R	Male 22-18 AWG 1/4" Tab	Clam	18	662381401601	10	50662381409268
M16-187-2V-10R	Male 16-14 AWG 1/4" Tab	Clam	10	662381401564	10	50662381409183
M16-187-2V-18R	Male 16-14 AWG 1/4" Tab	Clam	18	662381401625	10	50662381409305
M12-250-3V-8R	Male 12-10 AWG 1/4" Tab	Clam	8	662381401588	10	50662381409220
M12-250-3V-16R	Male 12-10 AWG 1/4" Tab	Clam	16	662381401649	10	50662381409343
P22-250-3V-50R	22-18 AWG Pairs	Clam	50	662381401656	10	50662381409367
P16-187-2V-50R	16-14 AWG Pairs	Clam	50	662381401663	10	50662381409381
P12-250-3V-50R	12-10 AWG Pairs	Clam	50	662381401670	10	50662381409404
MINITERM™ Butt Splice Terminals						
B22-V-10R	22-18 AWG	Clam	10	662381401359	10	50662381408940
B22-V-100R	22-18 AWG	Clam	100	662381401410	10	50662381409060
B16-V-10R	16-14 AWG	Clam	10	662381401366	10	50662381408964
B16-V-50R	16-14 AWG	Clam	50	662381401427	10	50662381409084
B12-V-8R	12-10 AWG	Clam	8	662381401373	10	50662381408988
B12-V-50R	12-10 AWG	Clam	50	662381401434	10	50662381409107

PRODUCT SET-UP INFORMATION

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.29	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.31	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.46	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.49	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.32	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.34	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.36	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.53	
1.77	4.13	0.06	8.07	2.13	4.53	0.04	0.57	
1.77	4.13	0.07	8.07	2.13	4.53	0.04	0.66	
2.87	4.61	0.19	14.25	3.15	4.92	0.13	1.89	
2.87	4.61	0.21	14.25	3.15	4.92	0.13	2.08	
2.87	4.61	0.31	14.25	3.15	4.92	0.13	3.14	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.42	
1.77	4.13	0.05	6.61	2.13	4.53	0.04	0.48	
1.77	4.13	0.05	6.61	2.13	4.53	0.04	0.52	
1.77	4.13	0.06	8.07	2.13	4.53	0.04	0.63	
1.77	4.13	0.08	8.07	2.13	4.53	0.04	0.80	
1.77	4.13	0.08	8.07	2.13	4.53	0.04	0.84	
2.87	4.61	0.19	14.25	3.15	4.92	0.13	1.92	
2.87	4.61	0.26	14.25	3.15	4.92	0.13	2.56	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.31	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.27	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.48	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.47	
2.87	4.61	0.18	14.25	3.15	4.92	0.13	1.80	
2.87	4.61	0.18	14.25	3.15	4.92	0.13	1.76	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.35	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.34	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.54	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.54	
2.87	4.61	0.21	14.25	3.15	4.92	0.13	2.12	
2.87	4.61	0.21	14.25	3.15	4.92	0.13	2.09	
1.77	4.13	0.05	6.61	2.13	4.53	0.04	0.47	
2.87	4.61	0.22	14.25	3.15	4.92	0.13	2.23	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.39	
1.77	4.13	0.07	8.07	2.13	4.53	0.04	0.65	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.36	
1.77	4.13	0.06	8.07	2.13	4.53	0.04	0.57	
1.77	4.13	0.05	6.61	2.13	4.53	0.04	0.47	
1.77	4.13	0.08	8.07	2.13	4.53	0.04	0.79	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.36	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.53	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.35	
1.77	4.13	0.05	8.07	2.13	4.53	0.04	0.52	
1.77	4.13	0.05	6.61	2.13	4.53	0.04	0.47	
1.77	4.13	0.08	8.07	2.13	4.53	0.04	0.79	
2.87	4.61	0.14	14.25	3.15	4.92	0.13	1.38	
2.87	4.61	0.13	14.25	3.15	4.92	0.13	1.30	
2.87	4.61	0.22	14.25	3.15	4.92	0.13	2.23	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.43	
2.87	4.61	0.30	14.25	3.15	4.92	0.13	2.95	
1.77	4.13	0.05	6.61	2.13	4.53	0.04	0.50	
2.87	4.61	0.20	14.25	3.15	4.92	0.13	2.03	
1.77	4.13	0.06	6.61	2.13	4.53	0.04	0.59	
2.87	4.61	0.30	14.25	3.15	4.92	0.13	3.00	

NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
MINITERM™ Female/Male Disconnect Terminals (Fully Insulated)						
IF22-250-3N-6R	Female 22-18 AWG 1/4" Tab	Clam	6	662381401779	10	50662381409428
IF22-250-3N-20PR	22-18 AWG Pairs	Clam	20	662381401830	10	50662381409541
IF16-250-3N-6R	Female 16-14 AWG 1/4" Tab	Clam	6	662381401793	10	50662381409466
IF16-250-3N-20PR	16-14 AWG Pairs	Clam	20	662381401847	10	50662381409565
IF12-250-3N-4R	Female 12-10 AWG 1/4" Tab	Clam	4	662381401816	10	50662381409503
IM22-250-3N-6R	Male 22-18 AWG 1/4" Tab	Clam	6	662381401786	10	50662381409442
IM16-250-3N-6R	Male 16-14 AWG 1/4" Tab	Clam	6	662381401809	10	50662381409480
IM12-250-3N-4R	Male 12-10 AWG 1/4" Tab	Clam	4	662381401823	10	50662381409527
P22-250-3N-50PR	22-18 AWG Pairs	Clam	50	662381401854	10	50662381409589
P16-250-3N-50PR	16-14 AWG Pairs	Clam	50	662381401861	10	50662381409602
P12-250-3N-30PR	12-10 AWG Pairs	Clam	30	662381401878	10	50662381409626
MINITERM™ Waterproof Terminals						
SR22-3R	Rings 22-18 AWG / 8-10 Stud- Waterproof	Clam	3	662381401977	10	50662381409640
SR16-3R	Rings 16-14 AWG / 8-10 Stud- Waterproof	Clam	3	662381401984	10	50662381409664
SR12-3R	Rings 12-10 AWG / 8-10 Stud- Waterproof	Clam	3	662381401991	10	50662381409688
SR12-14-3R	Rings 12-10 AWG / 1/4" Stud- Waterproof	Clam	3	662381402004	10	50662381409701
SS22-10-3R	Spades 22-18 AWG / 8-10 Stud- Waterproof	Clam	3	662381402011	10	50662381409725
SS16-10-3R	Spades 16-14 AWG / 8-10 Stud- Waterproof	Clam	3	662381402028	10	50662381409749
SS12-10-3R	Spades 12-10 AWG / 8-10 Stud- Waterproof	Clam	3	662381402035	10	50662381409763
SB22-3R	Butt Splices 22-18 AWG - Waterproof	Clam	3	662381402042	10	50662381409787
SB16-3R	Butt Splices- 16-14 AWG- Waterproof	Clam	3	662381402059	10	50662381409800
SB12-3R	Butt Splices- 12-10 AWG- Waterproof	Clam	3	662381402066	10	50662381409824
MINITERM™ Bullet Disconnect Terminals						
PMF22-157N-10PR	22-16 AWG Pairs	Clam	10	662381401885	10	50662381416303
PMF16-157N-20PR	16-14 AWG Pairs	Clam	20	662381401892	10	50662381416327
TERMINAL BLOKS™						
TB3096-6	Double Row Terminal Block 6 polls	Clam	6	662381165046	5	50662381992241
TB3096-8	Double Row Terminal Block 8 polls	Clam	4	662381165060	5	50662381992289
TB3096-10	Double Row Terminal Block 10 poles	Clam	4	662381165084	5	50662381992326
Terminal and Wire Connector Kits						
MTK-175	175 Ass't Terminals	Kit	175	662381400734	5	50662381414187
MTKL-100	100 Ass't Terminals & Crimping Tool	Kit	100	662381400789	5	50662381414286
MTKL-25	25 Ass't Terminals & Crimping Tool	Clam	25	662381400796	5	50662381414309
MTK-2218	46 Ass't Terminals 22-18 AWG	Clam	46	662381400741	10	50662381414200
MTK-1614	48 Ass't Terminals 16-14 AWG	Clam	48	662381400758	10	50662381414224
MTK-1210	28 Ass't Terminals 12-10 AWG	Clam	28	662381400765	10	50662381414248
MTK-32	32 Ass't Terminals & Wire Connectors	Clam	32	662381400802	10	50662381414323
MTK-80	80 Ass't Terminals	Kit	80	662381400772	5	50662381414262
Charging Clips						
BCL5-4R	5 Amp	Card	4	662381402578	10	50662381410127
BCL10-4R	10 Amp	Card	4	662381402585	10	50662381410141
BCL20-2R	20 Amp	Card	2	662381402592	10	50662381410165
BCL30-2R	30 Amp	Card	2	662381402608	10	50662381410189
BCL50-1R	50 Amp	Card	1	662381402615	10	50662381410202
Insulated Battery Clamps						
BCM10-2R	10 Amp, 1 Red and 1 Black	Card	2	662381402554	10	50662381410080
BCM30-2R	30 Amp, 1 Red and 1 Black	Card	2	662381402561	10	50662381410103
Alligator Clips						
ATC-125-4R	8-2 AWG Stranded	Card	4	662381402714	10	50662381410226
ATC-200-4R	8-0 AWG Solid or Stranded	Card	4	662381402721	10	50662381410240
ATC-1B-2R	2-00 AWG Stranded or Solid	Card	2	662381402738	10	50662381410264
ATC-2B-2R	6-0000 AWG Stranded	Card	2	662381402745	10	50662381410288
Wall/Switch Plate Screws						
WPB-10R	Brown	Card	10	662381402974	10	50662381410387
WPI-10R	Ivory	Card	10	662381402981	10	50662381410400
WPW-10R	White	Card	10	662381402998	10	50662381410424

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.36	
1.77	4.13	0.08	8.07	2.13	4.53	0.04	0.81	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.35	
1.77	4.13	0.08	8.07	2.13	4.53	0.04	0.80	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.35	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.36	
1.77	4.13	0.04	6.61	2.13	4.53	0.04	0.35	
1.77	4.13	0.03	6.61	2.13	4.53	0.04	0.35	
2.87	4.61	0.16	14.25	3.15	4.92	0.13	1.62	
2.87	4.61	0.15	14.25	3.15	4.92	0.13	1.54	
2.87	4.61	0.12	14.25	3.15	4.92	0.13	1.21	
1.77	4.13	0.02	6.46	2.05	4.65	0.04	0.24	
1.77	4.13	0.02	6.46	2.05	4.65	0.04	0.24	
1.77	4.13	0.03	6.46	2.05	4.65	0.04	0.30	
1.77	4.13	0.03	6.46	2.05	4.65	0.04	0.33	
1.77	4.13	0.02	6.46	2.05	4.65	0.04	0.23	
1.77	4.13	0.02	6.46	2.05	4.65	0.04	0.24	
1.77	4.13	0.03	6.46	2.05	4.65	0.04	0.32	
1.77	4.13	0.03	6.46	2.05	4.65	0.04	0.26	
1.77	4.13	0.03	6.46	2.05	4.65	0.04	0.27	
1.77	4.13	0.03	6.46	2.05	4.65	0.04	0.34	
1.77	4.13	0.04	6.46	2.05	4.65	0.04	0.39	
1.77	4.13	0.06	6.46	2.05	4.65	0.04	0.57	
0.86	6.81	0.77	6.32	4.77	9.07	0.16	4.26	
0.74	10.63	1.03	6.32	4.77	9.07	0.21	3.68	
0.89	10.63	1.41	6.32	4.77	9.07	0.21	4.45	
4.33	8.27	0.67	6.32	4.77	9.07	0.16	3.75	
4.53	10.75	1.03	6.32	5.01	11.21	0.21	5.69	
3.78	10.63	0.51	4.06	3.70	10.86	0.09	2.88	
2.91	6.81	0.12	7.04	3.10	5.49	0.07	1.32	
2.91	6.81	0.14	7.04	3.10	5.49	0.07	1.54	
2.91	6.81	0.14	7.04	3.10	5.49	0.07	1.48	
2.91	6.81	0.09	7.04	3.10	6.56	0.08	1.10	
4.33	8.27	0.48	6.32	4.77	9.07	0.16	2.91	
2.75	4.75	0.05	6.30	3.07	5.04	0.06	0.54	
2.75	4.75	0.05	9.25	3.07	5.04	0.08	0.71	
2.75	4.75	0.07	9.25	3.07	5.04	0.08	0.85	
2.75	4.75	0.07	12.05	3.07	5.04	0.11	1.18	
3.75	6.25	0.09	9.84	4.06	6.61	0.15	1.18	
2.75	4.75	0.04	9.25	3.07	5.04	0.08	0.63	
3.75	6.25	0.07	12.01	4.06	6.61	0.19	1.18	
2.75	4.75	0.02	6.57	3.07	5.04	0.06	0.33	
2.75	4.75	0.03	6.57	3.07	5.04	0.06	0.36	
2.75	4.75	0.03	9.25	3.07	5.04	0.08	0.45	
2.75	4.75	0.02	6.30	3.07	5.04	0.06	0.35	
1.97	3.94	0.04	3.15	2.36	4.33	0.02	0.40	
1.97	3.94	0.04	3.15	2.36	4.33	0.02	0.40	
1.97	3.94	0.04	3.15	2.36	4.33	0.02	0.40	

NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
Toggle Switches						
78 210 TS	ON-OFF SPST 3/4 HP	Clam	1	662381782106	5	50662381411902
78 120 TQ	ON-OFF SPST 3/4 HP	Clam	1	662381781208	5	50662381411926
78 200 TS	ON-ON SPDT 3/4 HP	Clam	1	662381782007	5	50662381411940
78 150 TS	ON-OFF SPST 3/4 HP	Clam	1	662381405494	5	50662381411964
78 160 TS	ON-OFF-ON SPDT 3/4 HP	Clam	1	662381781604	5	50662381411988
78 220 TS	ON-OFF DPST 1 1/2 HP	Clam	1	662381782205	5	50662381412008
78 270 TS	ON-ON DPDT 1 1/2 HP	Clam	1	662381782700	5	50662381412022
78 230 TS	ON-OFF-ON DPDT 1 1/2 HP	Clam	1	662381782304	5	50662381412046
78 015 TS	ON-OFF SPST Insulated Outdoor	Clam	1	662381780157	5	50662381412107
76 065 TS	76 065 TS 1 Clamshell	Clam	1	662381405746	5	50662381413807
78 150 TW	ON-OFF SPST 1/3 HP	Clam	1	662381781505	5	50662381412084
78 130 TS	ON-OFF SPST Short Ball	Clam	1	662381405586	5	50662381412145
Toggle Switch Weathertight Boots						
79 300 MSR	Rubber toggle switch covers	Clam	2	662381405579	5	50662381412121
Pull Chain Switches						
75 102 CW	OFF-ON SPST- Nickel	Clam	1	662381751027	5	50662381412268
75 101 CW	OFF-ON SPST- Brass	Clam	1	662381751010	5	50662381412282
75 110 CW	OFF-ON-ON SPDT- Brass	Clam	1	662381751102	5	50662381412305
75 111 CQ	OFF-ON-ON-ON SP3T- Brass	Clam	1	662381751119	5	50662381412329
Push Button Switches						
76 010 PW	ON-OFF SPST 1/3HP	Clam	1	662381760104	5	50662381412169
76 065 PS	PUSH-ON SPST- Black Button	Clam	1	662381760654	5	50662381412183
76 035 PS	PUSH-OFF SPST- Red Button	Clam	1	662381405616	5	50662381412206
76 056 PS	ON-OFF SPST- Nickel	Clam	1	662381405739	5	50662381413784
76 055 PS	ON-OFF SPST- Brass	Clam	1	662381405630	5	50662381412244
Rocker Switches						
77 140 RQ	ON-OFF SPST	Clam	1	662381771407	5	50662381412343
77 150 RQ	ON-OFF SPST- Lighted	Clam	1	662381771506	5	50662381412367
Rotary Switches						
77 340 RW	OFF-ON-ON SPST- Brass	Clam	1	662381773401	5	50662381412381
77 320 RW	OFF-ON-ON-ON DP3T- Brass	Clam	1	662381773203	5	50662381412404
Fish Tapes						
FTS50	50' Fish Tape	Card	1	662381016379	5	50662381412466
FTS100	100' Fish Tape	Card	1	662381406057	2	50662381413548
FTS25	25' Fish Tape	Card	1	662381406002	5	50662381414422
Wire Lubricant						
SWL-1QR	1 Quart Pulling Lubricant	Tube	1	662381406897	12	50662381413104
Conduit Benders						
CB50	1/2" Bender	Card	1	662381016256	20	50662381413562
CB75	3/4" Bender	Card	1	662381016263	15	50662381413586
CBH75	Handle for 1/2" Bender	Label	1	662381016287	3	50662381413609
Wire Strippers						
TL-ADJ5	Adjustable 4" Wire Stripper	Clam	1	662381406170	5	50662381412527
TL-WS6	10-20 AWG 6" Wire Stripper	Clam	1	662381406156	5	50662381412480
TL-6-1	Multifunction 8 1/2" Wire Stripper	Clam	1	662381406163	5	50662381412503
TL-5-1	Multifunction 9 1/2" Wire Stripper	Clam	1	662381406439	5	50662381412664
TL-AWS	Automatic Wire Stripper	Clam	1	662381406446	5	50662381414163
TL-RCR	Cable Jacker Ripper 4"	Clam	1	662381406422	10	50662381413500
TL-DC	Diagonal Cutting Pliers 6 1/2"	Clam	1	662381406309	5	50662381412602
TL-CCIH	Cable Cutter 8"	Clam	1	662381406279	5	50662381412541
TL-CRP	Cutter/Crimper 8"	Clam	1	662381406316	5	50662381412626
TL-LNP	Long-Nose Pliers/Crimper 6 1/2"	Clam	1	662381406293	5	50662381412589
TL-LP	Lineman's Pliers 7 1/2"	Clam	1	662381406286	5	50662381412565
TL-ISS	Electrician's Screwdriver Set	Clam	1	662381406415	5	50662381412640
Multitesters						
TES-MT12	12-Range Multitester	Clam	1	662381406736	5	50662381412848
TES-MT19	19-Range Multitester	Clam	1	662381406743	5	50662381412862
TES-MTBL	Analog Battery Tester	Clam	1	662381406750	10	50662381412886
TES-DT18	18-Range Digital Multitester	Clam	1	662381406804	5	50662381412909
TES-DCM	Clamp-On Multitester	Clam	1	662381406811	2	50662381414446

PRODUCT SET-UP INFORMATION

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.47	
2.94	4.63	0.10	8.07	3.15	4.88	0.07	0.50	
2.94	4.63	0.10	8.07	3.15	4.88	0.07	0.49	
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.47	
2.94	4.63	0.10	8.07	3.15	4.88	0.07	0.49	
2.94	4.63	0.11	8.07	3.15	4.88	0.07	0.56	
2.94	4.63	0.12	8.07	3.15	4.88	0.07	0.60	
2.94	4.63	0.12	8.07	3.15	4.88	0.07	0.60	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.41	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.40	
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.44	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.38	
2.94	4.63	0.05	8.07	3.15	4.88	0.07	0.27	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.42	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.41	
2.94	4.63	0.12	8.07	3.15	4.88	0.07	0.62	
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.46	
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.44	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.38	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.38	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.38	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.38	
2.94	4.63	0.06	8.07	3.15	4.88	0.07	0.29	
2.94	4.63	0.06	8.07	3.15	4.88	0.07	0.31	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.40	
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.43	
8.50	10.25	0.50	8.46	5.91	10.24	0.30	10.14	
14.96	1.77	4.19	12.13	15.20	5.67	0.60	13.67	
7.10	7.67	0.84	7.13	5.51	8.07	0.18	4.44	
3.00	10.25	2.25	13.00	10.00	10.75	0.81	27.52	
9.25	7.50	1.48	0.85	9.40	7.85	0.04	7.60	
12.00	7.50	1.75	0.85	12.40	7.85	0.05	9.20	
1.00	38.00	3.24	2.50	4.50	39.50	0.26	10.00	
4.06	7.67	0.08	7.87	4.37	3.07	0.06	0.99	
3.94	8.94	0.15	9.25	4.37	2.76	0.06	2.21	
3.94	10.55	0.13	10.83	4.37	3.15	0.09	2.40	
4.06	11.34	0.25	11.42	4.37	3.54	0.10	2.82	
3.50	11.34	0.62	11.42	4.37	5.35	0.15	4.88	
4.09	7.40	0.05	12.13	4.37	7.72	0.24	1.48	
4.13	9.25	0.42	9.45	4.37	3.35	0.08	2.18	
4.13	11.02	0.90	11.61	4.37	3.55	0.10	4.74	
4.13	11.42	0.66	11.61	4.37	3.55	0.10	3.62	
4.13	9.06	0.36	9.45	4.37	3.35	0.08	1.98	
4.13	10.24	0.71	10.43	4.37	3.55	0.09	3.64	
4.06	10.24	0.44	11.22	4.37	4.72	0.13	1.00	
3.74	7.68	0.31	8.00	4.25	8.00	0.16	1.54	
5.31	10.04	0.53	9.00	6.25	10.50	0.34	2.65	
3.74	7.68	0.31	7.75	4.25	8.00	0.15	1.54	
4.72	8.86	0.46	10.25	5.00	9.25	0.27	2.31	
4.21	8.74	0.50	9.57	5.12	4.33	0.80	1.38	

NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
Probe Testers						
TES-111	Twin Probe Tester 80-250 VAC	Clam	1	662381782106	5	50662381411902
TES-2	Twin Probe Tester 120 or 240 VAC	Clam	1	662381781208	5	50662381411926
TES-LVT	Twin Probe Low Volt Tester	Clam	1	662381782007	5	50662381411940
TES-CT	Continuity/Screwdriver Tester	Clam	1	662381405494	5	50662381411964
TES-SOL	Heavy Duty Solenoid tester	Clam	1	662381781604	5	50662381411988
TES-122	Plug-In Circuit Analyzer	Clam	1	662381782205	5	50662381412008
TES-131	Plug-In Circuit Analyzer with GFCI	Clam	1	662381782700	5	50662381412022
TES-NC	Non-Contact Tester	Clam	1	662381782304	5	50662381412046
TES-BT	Pocket Battery Tester	Clam	1	662381780157	5	50662381412107
TES-AUTO	Probe Auto Tester	Clam	1	662381405746	5	50662381413807
TES-CON	Probe Continuity Tester	Clam	1	662381781505	5	50662381412084
Standard Cable Ties						
418-40R	4" White 18 Lbs.	Bag	40	662381404657	25	50662381411223
840-20R	8" White 40 Lbs.	Bag	20	662381404664	25	50662381411247
1150-12R	11" White 50 Lbs.	Bag	12	662381404671	25	50662381411261
1450-8R	14" White 50 Lbs.	Bag	8	662381404688	25	50662381411285
418-100R	4" White 18 Lbs.	Bag	100	662381404794	10	50662381411506
840-100R	8" White 40 Lbs.	Bag	100	662381404800	10	50662381411520
1150-100R	11" White 50 Lbs.	Bag	100	662381404831	10	50662381411582
1450-100R	14" White 50 Lbs.	Bag	100	662381404848	10	50662381411605
850X	8" White 50 Lbs.	Bag	1000	662381361394	5	50662381416846
1150X	11" White 50 Lbs.	Bag	1000	662381361196	5	50662381416860
4180-30R	4" Black 18 Lbs.	Bag	30	662381404718	25	50662381411346
8400-15R	8" Black 40 Lbs.	Bag	15	662381404725	25	50662381411360
11500-8R	11" Black 50 Lbs.	Bag	8	662381404732	25	50662381411384
14500-8R	14" Black 50 Lbs.	Bag	8	662381404749	25	50662381411407
4180-100R	4" Black 18 Lbs.	Bag	100	662381404855	10	50662381411629
8400-100R	8" Black 40 Lbs.	Bag	100	662381404862	10	50662381411643
11500-100R	11" Black 50 Lbs.	Bag	100	662381404879	10	50662381411667
14500-100R	14" Black 50 Lbs.	Bag	100	662381404886	10	50662381411681
8500X	8" Black 50 Lbs.	Bag	1000	662381361400	5	50662381416884
11500X	11" Black 50 Lbs.	Bag	1000	662381361202	5	50662381416907
Heavy Duty Cable Ties						
15120-10R	15" White 120#	Bag	10	662381404619	5	50662381414927
18175-10R	18" White 175#	Bag	10	662381404633	10	50662381414965
21175-10R	21" White 175#	Bag	10	662381405272	10	50662381415009
24175-10R	24" White 175#	Bag	10	662381404695	5	50662381411308
36175-10R	36" White 175#	Bag	10	662381404701	5	50662381411322
48175-10R	48" White 175#	Bag	10	662381405197	5	50662381416402
8120	8" White 120#	Bag	100	662381346230	5	50662381416440
11120	11" White 120#	Bag	100	662381346490	5	50662381416464
14120	15" White 120#	Bag	100	662381346421	5	50662381416488
18175	18" White 175#	Bag	100	662381361165	5	50662381416501
151200-10R	15" Black 120#	Bag	10	662381404626	5	50662381414941
181750-10R	18" Black 175#	Bag	10	662381404640	10	50662381414989
211750-10R	21" Black 175#	Bag	10	662381405289	10	50662381415023
241750-10R	24" Black 175#	Bag	10	662381404756	5	50662381411421
361750-10R	36" Black 175#	Bag	10	662381404763	5	50662381411445
481750-10R	48" Black 175#	Bag	10	662381405203	5	50662381416426
81200	8" Black 120#	Bag	100	662381346223	5	50662381416525
111200	11" Black 120#	Bag	100	662381346483	5	50662381416549
141200	15" Black 120#	Bag	100	662381346414	5	50662381416563
181750	18" Black 175#	Bag	100	662381361158	5	50662381416587
Fluorescent Cable Ties						
418-16-25R	4" Orange 18 lbs.	Bag	25	662381405074	25	50662381414743
418-17-25R	4" Yellow 18 lbs.	Bag	25	662381405081	25	50662381414767
418-18-25R	4" Green 18 lbs.	Bag	25	662381405098	25	50662381414781
418-20-25R	4" Blue 18 lbs.	Bag	25	662381405104	25	50662381414804
418-AFT	4" Assorted 18 lbs.	Bag	100	662381405111	10	50662381414828
840-AFT	8" Assorted 50 lbs.	Bag	100	662381405128	10	50662381417041

PRODUCT SET-UP INFORMATION

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.47	
2.94	4.63	0.10	8.07	3.15	4.88	0.07	0.50	
2.94	4.63	0.10	8.07	3.15	4.88	0.07	0.49	
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.47	
2.94	4.63	0.10	8.07	3.15	4.88	0.07	0.49	
2.94	4.63	0.11	8.07	3.15	4.88	0.07	0.56	
2.94	4.63	0.12	8.07	3.15	4.88	0.07	0.60	
2.94	4.63	0.12	8.07	3.15	4.88	0.07	0.60	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.41	
2.94	4.63	0.08	8.07	3.15	4.88	0.07	0.40	
2.94	4.63	0.09	8.07	3.15	4.88	0.07	0.44	
2.76	7.09	0.03	7.48	2.99	2.99	0.04	0.76	
2.83	10.75	0.05	14.17	3.15	3.15	0.08	1.30	
2.76	14.17	0.06	14.17	3.15	3.15	0.08	1.54	
2.83	17.32	0.05	17.32	3.07	3.07	0.09	1.26	
2.76	7.09	0.08	7.48	2.99	2.99	0.04	0.76	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	14.17	0.51	14.17	4.49	4.49	0.17	5.14	
4.45	17.32	0.63	17.32	4.45	4.45	0.20	6.32	
13.00	11.25	3.30	14.17	6.00	15.50	0.20	16.50	
13.00	14.17	4.80	17.32	6.00	15.50	0.20	24.00	
2.76	7.09	0.02	7.48	2.99	2.99	0.04	0.57	
2.83	10.75	0.04	14.17	3.15	3.15	0.08	0.97	
2.76	14.17	0.04	14.17	3.15	3.15	0.08	1.03	
2.83	17.32	0.05	17.32	3.07	3.07	0.09	1.26	
2.76	7.09	0.08	7.48	2.99	2.99	0.04	0.76	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	14.17	0.51	14.17	4.49	4.49	0.17	5.14	
4.45	17.32	0.63	17.32	4.45	4.45	0.20	6.32	
13.00	11.25	3.30	14.17	6.00	15.50	0.20	16.50	
13.00	14.17	4.80	17.32	6.00	15.50	0.20	24.00	
2.83	17.32	0.13	17.32	3.07	4.92	0.15	1.40	
4.45	12.20	0.19	14.17	4.49	5.90	0.22	2.00	
4.45	12.20	0.19	14.17	4.49	5.90	0.22	2.00	
4.45	12.20	0.38	14.17	4.49	5.90	0.22	1.90	
4.45	14.17	0.48	14.17	4.49	5.90	0.22	2.40	
4.45	12.20	0.53	14.17	4.49	5.90	0.22	2.65	
14.50	13.50	0.60	14.17	10.00	15.00	0.22	12.00	
14.50	13.50	0.51	14.17	10.00	15.00	0.22	10.20	
14.50	13.50	1.28	17.32	10.00	22.00	0.22	25.60	
14.50	13.50	1.53	17.32	10.00	22.00	0.22	30.60	
2.83	17.32	0.13	17.32	3.07	4.92	0.15	1.40	
4.45	12.20	0.19	14.17	4.49	5.90	0.22	2.00	
4.45	12.20	0.19	14.17	4.49	5.90	0.22	2.00	
4.45	12.20	0.38	14.17	4.49	5.90	0.22	1.90	
4.45	14.17	0.48	14.17	4.49	5.90	0.22	2.40	
4.45	12.20	0.53	14.17	4.49	5.90	0.22	2.65	
14.50	13.50	0.60	14.17	10.00	15.00	0.22	12.00	
14.50	13.50	0.51	14.17	10.00	15.00	0.22	10.20	
14.50	13.50	1.28	17.32	10.00	22.00	0.22	25.60	
14.50	13.50	1.53	17.32	10.00	22.00	0.22	30.60	
2.76	7.09	0.02	7.48	2.99	2.99	0.04	0.57	
2.76	7.09	0.02	7.48	2.99	2.99	0.04	0.57	
2.76	7.09	0.02	7.48	2.99	2.99	0.04	0.57	
2.76	7.09	0.02	7.48	2.99	2.99	0.04	0.57	
2.76	7.09	0.08	7.48	2.99	2.99	0.04	0.76	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	

NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
Fluorescent Cable Ties Continued						
750-16	8" Orange 50 lbs.	Bag	100	662381353542	10	50662381416761
750-17	8" Yellow 50 lbs.	Bag	100	662381365118	10	50662381416785
750-18	8" Green 50 lbs.	Bag	100	662381353535	10	50662381416808
750-20	8" Blue 50 lbs.	Bag	100	662381353511	10	50662381416822
Colored Cable Ties						
840-1	8" Brown 40 lbs.	Bag	100	662381353399	10	50662381416600
840-2	8" Red 40 lbs.	Bag	100	662381353344	10	50662381416624
840-3	8" Orange 40 lbs.	Bag	100	662381353320	10	50662381416648
840-4	8" Yellow 40 lbs.	Bag	100	662381353313	10	50662381416662
840-5	8" Green 40 lbs.	Bag	100	662381353306	10	50662381416686
840-6	8" Blue 40 lbs.	Bag	100	662381353290	10	50662381416709
840-7	8" Purple 40 lbs.	Bag	100	662381353283	10	50662381416723
840-8	8" Grey 40 lbs.	Bag	100	662381353276	10	50662381416747
840-GR-20R	8" Green 40 lbs.	Bag	20	662381404787	25	50662381411483
840-AST-20R	8" Assorted 40 lbs.	Bag	20	662381404770	25	50662381411469
840-GR-100R	8" Green 40 lbs.	Bag	100	662381404824	10	50662381411568
840-AST-100R	8" Assorted 40 lbs.	Bag	100	662381404817	10	50662381411544
Releasable Cable Ties						
850-R-25R	8" White 50 lbs.	Bag	25	662381404893	10	50662381414842
1150-R-20R	11" White 50 lbs.	Bag	20	662381404954	10	50662381414880
850R	8" White 50 lbs.	Bag	100	662381353269	10	50662381416204
1050R	11" White 50 lbs.	Bag	100	662381359216	10	50662381416228
8500-R-25R	8" Black 50 lbs.	Bag	25	662381404909	10	50662381414866
11500-R-20R	11" Black 50 lbs.	Bag	20	662381404961	10	50662381414903
152500R-4R	15" Black 250 Lbs.	Bag	4	662381405234	10	50662381417539
212500R-4R	21" Black 250 Lbs.	Bag	3	662381405241	10	50662381417553
Mounting Cable Ties						
750MH-20R	8" White 50 lbs.	Bag	20	662381404985	25	50662381411742
7500MH-15R	8" Black 50 lbs.	Bag	15	662381404992	25	50662381411766
750MH-100R	8" White 50 lbs.	Bag	100	662381405005	10	50662381411704
7500MH-100R	8" Black 50 lbs.	Bag	100	662381405012	10	50662381411728
Metal Pawl Cable Ties						
750-SB	7.5" White 50 Lbs.	Bag	100	662381360212	10	50662381417720
7500-SB	7.5" Black 50 Lbs.	Bag	100	662381360205	10	50662381417737
1150-SB	11" White 50 Lbs.	Bag	100	662381360359	10	50662381417744
11500-SB	11" Black 50 Lbs.	Bag	100	662381360342	10	50662381417751
Beaded Releasable Cable Ties						
9700B-15R	9" Black	Bag	15	662381405043	25	50662381414583
970BG-15R	9" Green	Bag	15	662381405050	25	50662381414606
11700B-15R	11" Black	Bag	15	662381405166	25	50662381416143
1170BG-15R	11" Green	Bag	15	662381405173	25	50662381416167
Hook & Loop Cable Ties						
V850-5R	8" Black	Bag	5	662381405135	25	50662381411827
V1250-3R	12" Black	Bag	3	662381405142	25	50662381411841
Stainless Steel Cable Ties						
SS6100-10R	6" Silver 100 Lbs.	Bag	10	662381405258	10	50662381411865
SS11100-10R	11" Silver 100 Lbs.	Bag	10	662381405265	10	50662381411889
Cable Tie Adhesive Mounting Bases						
FTH5A-5R	1x1" White	Bag	5	662381405029	25	50662381411780
FTH5A-B-5R	1x1" Black	Bag	5	662381405036	25	50662381411803
Cable Tie Tightening Tool						
TRT-200	6 1/2" Trigger Pull Tool	Clam	1	662381405364	10	50662381413524
Cable Tie Canisters						
CTP-300BW	300 Piece Black & White	Tube	1	662381403469	12	50662381413906
CTP-500W	500 Piece White	Tube	1	662381403476	12	50662381413920
CTP-650	650 Piece Assorted Colors	Tube	1	662381091710	12	50662381340516

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
4.45	12.20	0.28	14.17	4.49	4.49	0.17	2.86	
4.45	12.20	0.28	14.17	4.49	4.49	0.17	2.86	
4.45	12.20	0.28	14.17	4.49	4.49	0.17	2.86	
4.45	12.20	0.28	14.17	4.49	4.49	0.17	2.86	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
2.83	10.75	0.05	14.17	3.15	3.15	0.08	1.30	
2.83	10.75	0.05	14.17	3.15	3.15	0.08	1.30	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
2.83	10.75	0.05	14.17	3.15	4.92	0.13	1.30	
2.76	14.17	0.06	14.17	3.15	4.92	0.13	1.54	
4.45	12.20	0.26	14.17	4.49	4.92	0.17	2.60	
4.45	12.20	0.26	14.17	4.49	4.92	0.17	2.60	
2.83	10.75	0.05	14.17	3.15	4.92	0.13	1.30	
2.76	14.17	0.06	14.17	3.15	4.92	0.13	1.54	
1.28	18.25	0.08	14.17	3.15	4.92	0.13	1.28	
1.28	18.25	0.09	14.17	3.15	4.92	0.13	1.30	
2.83	10.75	0.06	14.17	3.15	3.15	0.08	1.53	
2.83	10.75	0.05	14.17	3.15	3.15	0.08	1.15	
4.45	12.20	0.31	14.17	4.49	4.49	0.17	3.07	
4.45	12.20	0.31	14.17	4.49	4.49	0.17	3.07	
4.45	12.20	0.13	14.17	4.49	4.49	0.17	1.26	
4.45	12.20	0.13	14.17	4.49	4.49	0.17	1.26	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
4.45	12.20	0.26	14.17	4.49	4.49	0.17	2.59	
2.83	10.75	0.07	14.17	3.15	4.92	0.13	1.85	
2.83	10.75	0.07	14.17	3.15	4.92	0.13	1.85	
2.76	14.17	0.09	14.17	3.15	4.92	0.13	2.20	
2.76	14.17	0.09	14.17	3.15	4.92	0.13	2.20	
2.83	10.75	0.03	14.17	3.15	3.15	0.08	0.82	
2.76	14.17	0.03	14.17	3.15	3.15	0.08	0.68	
2.83	10.75	0.05	14.17	3.15	3.15	0.08	0.49	
2.76	14.17	0.07	14.17	3.15	3.15	0.08	0.74	
2.76	7.09	0.02	7.48	2.99	2.99	0.04	0.49	
2.76	7.09	0.02	7.48	2.99	2.99	0.04	0.49	
4.09	9.25	1.25	9.53	4.37	9.61	0.23	12.50	
2.25	8.38	0.36	9.75	7.50	8.50	-	3.58	
2.78	8.13	0.76	8.50	7.50	8.50	-	9.65	
1.18	10.00	1.12	10.25	13.00	10.25	-	15.10	

NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
Low Volt Staples						
BWSP-187-25R	3/16" White	Clam	25	662381403803	10	50662381410905
BWSP-187-100R	3/16" White	Clam	100	662381403810	10	50662381410929
BWSP-1870-25R	3/16" Black	Clam	25	662381403827	10	50662381410943
BWSP-1870-100R	3/16" Black	Clam	100	662381403834	10	50662381410967
One Hole Cable Clamps						
NC-250N-18R	1/4" White	Clam	18	662381404053	10	50662381410981
NC-375N-15R	3/8" White	Clam	15	662381404060	10	50662381411001
NC-500N-12R	1/2" White	Clam	12	662381404077	10	50662381411025
NC-750N-6R	3/4" White	Clam	6	662381404084	10	50662381411049
NC-1000N-4R	1" White	Clam	4	662381404091	10	50662381411063
NC-250B-18R	1/4" Black	Clam	18	662381404107	10	50662381411087
NC-375B-15R	3/8" Black	Clam	15	662381404114	10	50662381411100
NC-500B-12R	1/2" Black	Clam	12	662381404121	10	50662381411124
NC-750B-6R	3/4" Black	Clam	6	662381404138	10	50662381411148
NC-1000B-4R	1" Black	Clam	4	662381404145	10	50662381411162
Floor Cable Duct						
FD250W	FD250W 2 1/2" Off white 18' roll	Box	1	662381164001	1	662381164001
FD250B	FD250B 2 1/2" Brown 18' roll	Box	1	662381164018	1	662381164018
Metal Staples						
MS50-24R	1/2" For 14/2, 12/2, 10/2	Clam	24	662381404381	10	50662381412923
MS50-100R	3/4" for 14/2, 12/2, 10/2	Clam	100	662381404404	10	50662381412961
MS75-18R	1/2" for 14/3, 12/3, 10/3	Clam	18	662381404398	10	50662381412947
MS75-100R	3/4" for 14/3, 12/3, 10/3	Clam	100	662381404411	10	50662381412985
Insulated Metal Staples						
MSI50-15R	1/2" For 14/2, 12/2, 10/2	Clam	15	662381404428	10	50662381413005
MSI50-100R	1/2" For 14/2, 12/2, 10/2	Clam	100	662381404435	10	50662381413029
Coaxial Cable Staples						
PNC-157W-25R	1/4" White for RG-59/RG-6	Clam	25	662381403551	10	50662381410769
PNC-157W-50R	1/4" White for RG-59/RG-7	Clam	50	662381403568	10	50662381410783
PNC-157B-25R	1/4" Black for RG-59/RG-8	Clam	25	662381403575	10	50662381410806
PNC-157B-50R	1/4" Black for RG-59/RG-9	Clam	50	662381403582	10	50662381410820
Spiral Wrap						
SRPE-750	3/4" wide x 3 1/2' White	Bag	1	662381096067	10	50662381410448
Duct Seal						
DS184-R	Gray Pug 1 Lb.	Box	1	662381055279	5	50662381413142
Circuit Breaker Identifiers						
WMB-LC	Peel-Off 1/4" x 1" Markers	Clam	90	662381405814	10	50662381412428
Heat Shrink Tubing						
TWHS-093-4-8R	3/32" to 3/64"	Bag	8	662381403216	10	50662381410509
TWHS-125-4-7R	1/8" to 1/16"	Bag	7	662381403223	10	50662381410523
TWHS-187-4-8R	3/16" to 3/32"	Bag	8	662381403230	10	50662381410547
TWHS-250-4-6R	1/4" to 1/8"	Bag	6	662381403247	10	50662381410561
TWHS-375-4-3R	3/8" to 3/16"	Bag	3	662381403254	10	50662381410585
TWHS-500-4-3R	1/2" to 1/4"	Bag	3	662381403261	10	50662381410608
TWHS-750-4-2R	3/4" to 3/8"	Bag	2	662381403278	10	50662381410622
TWHS-1000-4-2R	1" to 1/2"	Bag	2	662381403285	10	50662381410646
THK-AST-8R	Assorted Pack	Bag	8	662381403292	10	50662381410660
Underground Cable Splice Kits						
SKDB-R	8" with Brass 4-Coupler 8-14 AWG	Clam	1	662381403308	5	50662381413043
SKCB-2-R	4" with Brass 2-Coupler 8-2 AWG	Clam	1	662381403315	5	50662381413067
SKCB-8-R	4" with Brass 2-Coupler 8-14 AWG	Clam	1	662381403322	5	50662381413081
WAGS-4/0-4	Gel-Filled Wrap 14-4/0 AWG 120 V	Clam	1	662381015716	5	50662381417591
ESGTS-2	Gel-Filled Wrap 14-2 AWG 12 V	Clam	1	662381168634	5	50662381417577
Liquid Electrical Tape						
LETB-4	Black 4 oz.	Can	1	662381404572	5	50662381415986
LETR-4	Red 4 oz.	Can	1	662381404589	5	50662381416006
LETW-4	White 4 oz.	Can	1	662381404596	5	50662381416020

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
1.77	4.13	0.05	8.27	2.17	4.53	0.05	0.46	
2.87	4.61	0.18	14.17	3.15	4.92	0.13	1.84	
1.77	4.13	0.05	8.27	2.17	4.53	0.05	0.46	
2.87	4.61	0.18	14.17	3.15	4.92	0.13	1.84	
2.87	4.61	0.02	14.17	3.15	4.92	0.13	0.21	
2.87	4.61	0.04	14.17	3.15	4.92	0.13	0.39	
2.87	4.61	0.04	14.17	3.15	4.92	0.13	0.37	
2.87	4.61	0.03	14.17	3.15	4.92	0.13	0.26	
2.87	4.61	0.02	14.17	3.15	4.92	0.13	0.22	
2.87	4.61	0.02	14.17	3.15	4.92	0.13	0.21	
2.87	4.61	0.04	14.17	3.15	4.92	0.13	0.39	
2.87	4.61	0.04	14.17	3.15	4.92	0.13	0.37	
2.87	4.61	0.03	14.17	3.15	4.92	0.13	0.26	
2.87	4.61	0.02	14.17	3.15	4.92	0.13	0.22	
2.60	0.60	1.99	6.00	12.00	6.25	-	2.70	
2.60	0.60	1.99	6.00	12.00	6.25	-	2.70	
2.94	4.63	0.15	14.17	3.15	4.92	0.13	1.71	
2.87	4.61	0.59	14.17	3.15	4.92	0.13	6.17	
2.94	4.63	0.13	14.17	3.15	4.92	0.13	1.59	
2.87	4.61	0.74	14.17	3.15	4.92	0.13	7.65	
2.94	4.63	0.12	14.17	3.15	4.92	0.13	1.45	
2.87	4.61	0.34	14.17	3.15	4.92	0.13	3.65	
1.77	4.13	0.07	8.27	2.17	4.53	0.05	0.72	
2.87	4.61	0.14	14.17	3.15	4.92	0.13	1.43	
1.77	4.13	0.07	8.27	2.17	4.53	0.05	0.72	
2.87	4.61	0.14	14.17	3.15	4.92	0.13	1.43	
5.91	14.17	0.14	14.17	5.91	12.99	0.63	1.39	
2.25	1.25	1.00	6.00	8.75	3.00	-	5.25	
2.94	4.63	0.15	14.17	3.15	4.92	0.13	1.60	
2.76	7.09	0.01	7.48	2.99	4.92	0.06	0.08	
2.76	7.09	0.01	7.48	2.99	4.92	0.06	0.08	
2.76	7.09	0.01	7.48	2.99	4.92	0.06	0.13	
2.76	7.09	0.02	7.48	2.99	4.92	0.06	0.20	
2.76	7.09	0.01	7.48	2.99	4.92	0.06	0.12	
2.76	7.09	0.02	7.48	2.99	4.92	0.06	0.16	
2.76	7.09	0.02	7.48	2.99	4.92	0.06	0.18	
2.76	7.09	0.03	7.48	2.99	4.92	0.06	0.26	
2.76	7.09	0.03	7.48	2.99	4.92	0.06	0.27	
2.75	9.00	0.20	0.80	3.00	9.50	0.01	1.00	
2.75	9.00	0.12	0.80	3.00	9.50	0.01	0.65	
2.75	9.00	0.12	0.80	3.00	9.50	0.01	0.65	
2.75	9.00	0.19	0.80	3.00	9.50	0.01	5.03	
2.75	9.00	0.19	0.80	3.00	9.50	0.01	5.03	
4.50	8.00	-	-	-	-	-	-	
4.50	8.00	-	-	-	-	-	-	
4.50	8.00	-	-	-	-	-	-	

NSI RETAIL PRODUCT SET-UP INFORMATION

MODEL NUMBER	DESCRIPTION	SALE PACK TYPE	SALE PACK QTY.	SALE PACK UPC	CARTON PACK QTY	CARTON PACK 1 2 OF 5
EASY-WRAP™ Electrical Tape						
EWG 7030	30' x 3/4" Black	Roll	1	662381404527	250	662381404527
EWG 7060-LL	60' x 3/4" Black	Roll	1	662381404534	200	662381404534
EWG 7060-1	60' x 3/4" Brown	Roll	1	662381706010	200	662381706010
EWG 7060-2	60' x 3/4" Red	Roll	1	662381706027	200	662381706027
EWG 7060-3	60' x 3/4" Orange	Roll	1	662381706034	200	662381706034
EWG 7060-4	60' x 3/4" Yellow	Roll	1	662381706041	200	662381706041
EWG 7060-5	60' x 3/4" Green	Roll	1	662381706058	200	662381706058
EWG 7060-6	60' x 3/4" Blue	Roll	1	662381706065	200	662381706065
EWG 7060-7	60' x 3/4" Violet	Roll	1	662381706072	200	662381706072
EWG 7060-9	60' x 3/4" White	Roll	1	662381706096	200	662381706096
EASY-WRAP™ Premium Electrical Tape						
EWP 7066	66' x 3/4" Black in plastic puck	Puck	1	662381706607	100	662381788665
EWP 7066-1	66' x 3/4" Brown in plastic puck	Puck	1	662381706614	100	662381788689
EWP 7066-2	66' x 3/4" Red in plastic puck	Puck	1	662381706621	100	662381788702
EWP 7066-3	66' x 3/4" Orange in plastic puck	Puck	1	662381706638	100	662381788726
EWP 7066-4	66' x 3/4" Yellow in plastic puck	Puck	1	662381706645	100	662381788740
EWP 7066-5	66' x 3/4" Green in plastic puck	Puck	1	662381706652	100	662381788764
EWP 7066-6	66' x 3/4" Blue in plastic puck	Puck	1	662381706669	100	662381788788
EWP 7066-7	66' x 3/4" Violet in plastic puck	Puck	1	662381706676	100	662381788801
EWP 7066-9	66' x 3/4" White in plastic puck	Puck	1	662381706690	100	662381788849
Colored Tape Assortment						
EWG-ASTCR-5R	1/2" wide x 12' Red, White, Blue, Green, Yellow	Clam	1	662381400772	5	50662381414422
EASY-WRAP™ FrictionTape						
EWFT 157560	3/4" wide x 60' long Black	Clam	1	662381706812	10	50662381415863
EASY-WRAP™ Self-Bonding Fusion Tape						
EWSR 121010	1" Wide x 10' Long Black	Clam	1	662381404602	5	50662381414569
Ratcheting Cable Clamps						
RCC-1-50	Small 1" Capacity in Display Box	Box	50	662381405296	1	50662381416082
RCC-2-34	Medium 2" Capacity in Display Box	Box	34	662381405302	1	50662381416105
RCC-3-25	Large 3" Capacity in Display Box	Box	25	662381405319	1	50662381416129

	PRODUCT DIMENSIONS AND WEIGHTS							
	SALE PACK			CARTON PACK				
	WIDTH (INCH)	HEIGHT (INCH)	WEIGHT (LBS.)	DEPTH (INCH)	WIDTH (INCH)	HEIGHT (INCH)	CUBE (SQ. IN.)	WEIGHT (LBS.)
	2.28	0.75	0.09	12.60	12.60	8.67	0.80	23.10
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	2.87	0.75	0.17	15.35	12.40	8.67	0.95	36.30
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	23.32
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	22.00
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	22.00
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	22.00
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	22.00
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	22.00
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	22.00
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	22.00
	3.58	0.90	0.24	20.00	8.46	10.24	0.89	22.00
	1.57	1.57	0.09	9.45	4.13	4.33	0.10	2.51
	3.50	3.50	0.29	-	-	-	-	-
	2.95	4.63	0.14	8.07	3.12	4.87	-	0.85
	5.00	4.50	1.26	7.25	5.75	5.50	-	1.54
	5.00	4.50	2.11	7.25	5.75	5.50	-	2.35
	5.00	8.12	3.02	7.5	5.50	9.00	-	3.36

ALPHABETICAL INDEX BY PRODUCT NAME

Acorn Clamp for 1/2" Pipe	10	Coaxial Staples 1/4" Black	46
Acorn Clamp for 5/8" Pipe	10	Coaxial Staples 1/4" White	46
Alligator Clips	17	Colored Cable Ties - 8"	40
Aluminum Anti-Oxidants	11	Colored Cable Ties - 8" Assorted	40
Aluminum Mechanical Lugs	11	Conduit Bender - 1/2"	23
Aluminum Split Bolts	11	Conduit Bender - 3/4"	23
Battery Clamp 10 Amp, 1 Red and 1 Black	17	Conduit Bender Handle	23
Battery Clamp 30 Amp, 1 Red and 1 Black	17	Continuity/Screwdriver Tester	34
Battery Tester - Analog	31	Copper Mechanical Lugs	11
Battery Tester - Pocket	36	Copper Split Bolts	11
Bullet Disconnects - 16-14 AWG Pairs	15	Crimp Sleeves	10
Bullet Disconnects - 22-16 AWG Pairs	15	Cutter/Crimper 8"	27
Butt Splices	14	Diagonal Cutting Pliers 6 1/2"	27
Butt Splices - Waterproof	15	Double Row Terminal Blocks	15
Cable Cutter 8"	27	Duct Seal Gray Pug 1 Lb.	47
Cable Jacker Ripper 4'	26	Electrical Tape - 60' x 3/4"	49
Cable Tie Canisters	42	Electrical Tape - Black - 30' x 3/4"	49
Cable Tie Tightening Tool	41	Electrical Tape - Premium - 66' x 3/4"	49
Cable Ties - Beaded 11"	41	Electrical Tapes - Assorted - 1/2" x 12'	49
Cable Ties - Beaded 9"	41	Electrician's Screwdriver Set	28
Cable Ties - Heavy Duty 11" 120 Lbs.	39	Female Disconnects - 12-10 AWG	14
Cable Ties - Heavy Duty 15" 120 Lbs.	39	Female Disconnects - 16-14 AWG	14
Cable Ties - Heavy Duty 18" 175 Lbs.	39	Female Disconnects - 16-14 AWG	14
Cable Ties - Heavy Duty 21" 175 Lbs.	39	Female Disconnects - 22-18 AWG	14
Cable Ties - Heavy Duty 24" 175 Lbs.	39	Female/Male Disconnect Pairs - 12-10 AWG	14
Cable Ties - Heavy Duty 36" 175 Lbs.	39	Female/Male Disconnect Pairs - 16-14 AWG	14
Cable Ties - Heavy Duty 48" 175 Lbs.	39	Female/Male Disconnect Pairs - 22-18 AWG	14
Cable Ties - Heavy Duty 8" 120 Lbs.	39	Fish Tape - 100'	23
Cable Ties - Heavy Duty UV 11" 120 Lbs.	39	Fish Tape - 25'	23
Cable Ties - Heavy Duty UV 15" 120 Lbs.	39	Fish Tape 50'	23
Cable Ties - Heavy Duty UV 18" 175 Lbs.	39	Floor Cable Duct - Brown	45
Cable Ties - Heavy Duty UV 21" 175 Lbs.	39	Floor Cable Duct - Off white	45
Cable Ties - Heavy Duty UV 24" 175 Lbs.	39	Fluorescent Cable Ties - 4"	40
Cable Ties - Heavy Duty UV 36" 175 Lbs.	39	Fluorescent Cable Ties - 4" Assorted	40
Cable Ties - Heavy Duty UV 48" 175 Lbs.	39	Fluorescent Cable Ties - 8"	40
Cable Ties - Heavy Duty UV 8" 120 Lbs.	39	Fluorescent Cable Ties - 8" Assorted	40
Cable Ties - Metal Pawl 11" - Black	41	Friction Tape - 3/4" x 60'	49
Cable Ties - Metal Pawl 11" - White	41	Fusion Tape - 1" x 10'	49
Cable Ties - Metal Pawl 7.5" - Black	41	Ground Clamp for 1/2" - 1" Pipe	10
Cable Ties - Metal Pawl 7.5" - White	41	Grounding Clips 100 pack	10
Cable Ties - Mounting 8" Black	40	Grounding Clips 8 pack	10
Cable Ties - Mounting 8" White	40	Grounding Pigtails 2 pack	10
Cable Ties - Releasable 11" Black	40	Grounding Pigtails 50 pack	10
Cable Ties - Releasable 11" White	40	Grounding Screws 100 pack	10
Cable Ties - Releasable 15" Black	40	Grounding Screws 12 pack	10
Cable Ties - Releasable 21" Black	40	Grounding Wing Connectors - Green	9
Cable Ties - Releasable 8" Black	40	Heavy Duty Solenoid tester	34
Cable Ties - Releasable 8" White	40	Heat Shrink Tubing	48
Cable Ties - Stainless Steel 11"	41	Heat Shrink Tubing Assorted Pack	48
Cable Ties - Stainless Steel 6"	41	Hook and Loop Cable Ties - 12"	41
Cable Ties - Standard 11" White	39	Hook and Loop Cable Ties - 8"	41
Cable Ties - Standard 14" White	39	Insulated Metal Staples - 1/2"	46
Cable Ties - Standard 4" White	39	Lineman's Pliers 7 1/2"	28
Cable Ties - Standard 8" White	39	Liquid Electrical Tape Black 4 oz.	47
Cable Ties - Standard UV 11"	39	Liquid Electrical Tape Red 4 oz.	47
Cable Ties - Standard UV 14"	39	Liquid Electrical Tape White 4 oz.	47
Cable Ties - Standard UV 4"	39	Long-Nose Pliers/Crimper 6 1/2"	28
Cable Ties - Standard UV 8"	39	Low Volt Staples - 3/16" - Black	45
Charging Clips	17	Low Volt Staples - 3/16" - White	45
Circuit Analyzer - Plug-In	35	Male Disconnects - 12-10 AWG	14
Circuit Analyzer with GFCI - Plug-In	35	Male Disconnects - 16-14 AWG	14

Male Disconnects - 22-18 AWG	14	Switches - Push Button - 1/3HP	20
Metal Staples - 1/2"	46	Switches - Push Button - Black Button	20
Metal Staples - 3/4"	46	Switches - Push Button - Brass	20
Mounting Bases - 1x1" - Black	41	Switches - Push Button - Nickel	20
Mounting Bases - 1x1" - White	41	Switches - Push Button - Red Button	20
Multitester - 12-Range	31	Switches - Rocker	20
Multitester - 19-Range	31	Switches - Rocker - Lighted	20
Multitester - Clamp-On	32	Switches - Rotary - Brass	20
Multitester - Digital - 18-Range	32	Switches - Rubber toggle switch covers	19
Non-Contact Tester	36	Switches - Toggle - 1 1/2 HP	19
Nylon Pigtails - 12-10 AWG	10	Switches - Toggle - 1/3 HP	19
Nylon Pigtails - 16-14 AWG	10	Switches - Toggle - 3/4 HP	19
Nylon Pigtails - 22-16 AWG	10	Switches - Toggle - Bat Lever	19
One Hole Cable Clamp - 1" - Black	45	Switches - Toggle - DPDT - 1 1/2 HP	19
One Hole Cable Clamp - 1" - White	45	Switches - Toggle - Insulated Outdoor	19
One Hole Cable Clamp - 1/2" - Black	45	Switches - Toggle - Short Ball	19
One Hole Cable Clamp - 1/2" - White	45	Switches - Toggle - SPDT - 3/4 HP	19
One Hole Cable Clamp - 1/4" - Black	45	Terminals Kits	16
One Hole Cable Clamp - 1/4" - White	45	Wall Plate Screws - Brown	17
One Hole Cable Clamp - 3/4" - Black	45	Wall Plate Screws - Ivory	17
One Hole Cable Clamp - 3/4" - White	45	Wall Plate Screws - White	17
One Hole Cable Clamp - 3/8" - Black	45	Wing Connectors - Assorted	8
One Hole Cable Clamp - 3/8" - White	45	Wing Wire Connectors - Blue	8
Probe Auto Tester	35	Wing Wire Connectors - Gray	8
Probe Continuity Tester	35	Wing Wire Connectors - Red	8
Probe Low Volt Tester - Twin	33	Wing Wire Connectors - Tan	8
Probe Tester - Twin - 120 or 240 VAC	33	Wing Wire Connectors - Yellow	8
Probe Tester - Twin - 80-250 VAC	33	Wire Connector - Assorted	7
Pulling Lubricant - 1 Quart	23	Wire Connector - Orange	7
Push-In Connector 2 PORT	9	Wire Connector - Yellow	7
Push-In Connector 2 PORT 100 pack	9	Wire Connectors - Blue	7
Push-In Connector 3 PORT	9	Wire Connectors - Gray	7
Push-In Connector 3 PORT 100 pack	9	Wire Connectors - Red	7
Push-In Connector 4 PORT	9	Wire Markers - Peel-Off 1/4" x 1"	47
Push-In Connector 4 PORT 100 pack	9	Wire Stripper - 6" - 10-20 AWG	25
Push-In Connector 8 PORT	9	Wire Stripper - 8 1/2"	25
Push-In Connector 8 PORT 50 pack	9	Wire Stripper - 9 1/2"	26
Ratchet Clamp - Large 3"	50	Wire Stripper - Adjustable 4"	25
Ratchet Clamp - Medium 2"	50	Wire Stripper - Automatic	26
Ratchet Clamp - Small 1"	50		
Rings Terminals - 12-10 AWG	13		
Rings Terminals - 12-10 AWG - Waterproof	15		
Rings Terminals - 16-14 AWG	13		
Rings Terminals - 16-14 AWG - Waterproof	15		
Rings Terminals - 22-18 AWG	13		
Rings Terminals - 22-18 AWG - Waterproof	15		
Spade Terminals - 12-10 AWG	13		
Spade Terminals - 12-10 AWG - Waterproof	15		
Spade Terminals - 16-14 AWG	13		
Spade Terminals - 16-14 AWG - Waterproof	15		
Spade Terminals - 22-18 AWG	13		
Spade Terminals - 22-18 AWG - Waterproof	15		
Spiral Wrap 3/4" x 3 1/2'	47		
Splice Kit 4" with Brass 2-Coupler 8-14 AWG	48		
Splice Kit 4" with Brass 2-Coupler 8-2 AWG	48		
Splice Kit 8" with Brass 4-Coupler 8-14 AWG	48		
Splice Kit Gel-Filled Wrap 14-2 AWG 12 V	48		
Splice Kit Gel-Filled Wrap 14-4/0 AWG 120 V	48		
Splicer/Reducers	11		
Switches - Pull Chain - Brass	19		
Switches - Pull Chain - Nickel	19		

INDEX BY PART NUMBER

8120.....39	75 110 CW19	9700B-15R41	EWP 7066-1.....49	MTKL-10016
11120.....39	75 111 CQ19	970BG-15R41	EWP 7066-2.....49	MTKL-2516
14120.....39	750-1640	APS02R11	EWP 7066-4.....49	N-1/OR11
18175.....39	750-1740	APS11R11	EWP 7066-5.....49	N-2/OR11
81200.....39	750-1840	APS21R11	EWP 7066-6.....49	N-2R11
111200.....39	750-2040	APS41R11	EWP 7066-7.....49	N-3/OR11
141200.....39	7500MH-100R40	ATC-125-4R17	EWP 7066-9.....49	N-4R11
181750.....39	7500MH-15R40	ATC-1B-2R17	EWSR 12101049	N-6R11
WC-0-CJ7	750MH-100R40	ATC-200-4R17	F12-250-3V-16R ...14	N-8R11
1/O-SRR11	750MH-20R40	ATC-2B-2R17	F12-250-3V-8R14	NC-1000B-4R45
1050R40	76 010 PW20	B12-V-50R14	F16-187-2V-10R ...14	NC-1000N-4R45
1140-SB41	76 035 PS20	B12-V-8R14	F16-187-2V-20R ...14	NC-250B-18R45
11400-SB41	76 055 PS20	B16-V-10R14	F22-250-3V-10R ...14	NC-250N-18R45
1150-100R39	76 056 PS20	B16-V-50R14	F22-250-3V-21R ...14	NC-375B-15R45
1150-12R39	76 065 PS20	B22-V-100R14	FD250B45	NC-375N-15R45
1150-R-20R40	76 065 TS19	B22-V-10R14	FD250W45	NC-500B-12R45
11500-100R39	77 140 RQ20	BCL10-4R17	FTH5A-5R41	NC-500N-12R45
11500-8R39	77 150 RQ20	BCL20-2R17	FTH5A-B-5R41	NC-750B-6R45
11500-R-20R40	77 320 RW20	BCL30-2R17	FTS10023	NC-750N-6R45
11500X39	77 340 RW20	BCL5-4R17	FTS2523	OX-1-1R11
1150X39	78 015 TS19	BCL50-1R17	FTS5023	OX-411
11700B-15R41	78 120 TQ19	BCM10-2R17	GGC-1000-8R10	P12-250-3N-30PR ..14
1170BG-15R41	78 130 TS19	BCM30-2R17	GRC-50R10	P12-250-3V-50R ...14
1450-100R39	78 150 TS19	BWSP-187-100R45	GRC-58R10	P16-187-2V-50R ...14
1450-8R39	78 150 TW19	BWSP-187-25R45	GSC10	P16-250-3N-50PR...14
14500-100R39	78 160 TS19	BWSP-1870-100R ..45	GSC-12R10	P22-250-3N-50PR ..14
14500-8R39	78 200 TS19	BWSP-1870-25R45	GZ-1R10	P22-250-3V-50R ...14
15120-10R39	78 210 TS19	C12-N-8R10	IF12-250-3N-4R ...14	PG12SC10
151200-10R39	78 220 TS19	C16-N-10R10	IF16-250-3N-20PR .14	PG12C-2R10
152500R-4R40	78 230 TS19	C22-N-10R10	IF16-250-3N-6R ...14	PIWC-29
18175-10R39	78 270 TS19	CB5023	IF22-250-3N-20PR .14	PIWC-2-10R9
181750-10R39	79 300 MSR19	CB7523	IF22-250-3N-6R ...14	PIWC-39
2-SRR11	750-SB41	CBH7523	IM12-250-3N-4R ...14	PIWC-3-10R9
2/OTR11	7500-SB41	CTP-300BW42	IM16-250-3N-6R ...14	PIWC-49
21175-10R39	840-140	CTP-500W42	IM22-250-3N-6R ...14	PIWC-4-10R9
211750-10R39	840-100R39	CTP-65042	LETB-447	PIWC-89
212500R-4R40	840-240	DE703R11	LETR-447	PIWC-8-5R9
24175-10R39	840-20R39	DE704R11	LETW-447	PMF16-157N-20PR..15
241750-10R39	840-340	DE705R11	M12-250-3V-16R ...14	PMF22-157N-10PR..15
2TR11	840-440	DE706R11	M12-250-3V-8R ...14	PNC-157B-25R46
36175-10R39	840-540	DS184-R47	M16-187-2V-10R ...14	PNC-157B-50R46
361750-10R39	840-640	ESGTS-248	M16-187-2V-18R ...14	PNC-157W-25R46
4/O-SRR11	840-740	EWFT 157560.....49	M22-250-3V-10R ...14	PNC-157W-50R46
418-100R39	840-840	EWG 703049	M22-250-3V-18R ...14	R12-14V-14R13
418-16-25R40	840-AFT40	EWG 7060-149	MS50-100R46	R12-14V-50R13
418-17-25R40	840-AST-100R40	EWG 7060-249	MS50-24R46	R12-14V-7R13
418-18-25R40	840-AST-20R40	EWG 7060-349	MS75-100R46	R12-38V-13R13
418-20-25R40	840-GR-100R40	EWG 7060-449	MS75-18R46	R12-38V-7R13
418-40R39	840-GR-20R40	EWG 7060-549	MSI50-100R46	R12-8V-14R13
418-AFT40	840-GR-20R40	EWG 7060-649	MSI50-15R46	R12-8V-50R13
4180-100R39	8400-100R39	EWG 7060-749	MTK-121016	R12-8V-8R13
4180-30R39	8400-15R39	EWG 7060-949	MTK-161416	R16-14V-100R13
48175-10R39	850-R-25R40	EWG 7060-949	MTK-17516	R16-14V-17R13
481750-10R39	8500R39	EWG 7060-LL49	MTK-221816	R16-14V-7R13
75 101 CW19	850R40	EWG-ASTCR-5R49	MTK-3216	R16-6V-100R13
75 102 CW19	850X39	EWP 706649	MTK-8016	R16-6V-10R13
		EWP 7066 349		

R16-6V-22R13	SB22-3R.....15	TES-MTBTL31	WC-B-14R7	WWC-B-10R.....8
R16-8V-100R13	SKCB-2-R.....48	TES-NC36	WC-B-25R7	WWC-B-2R.....8
R16-8V-10R13	SKCB-8-R.....48	TES-SOL34	WC-B-B7	WWC-B-B.....8
R16-8V-22R13	SKDB-R48	THK-AST-8R48	WC-B-C7	WWC-B-C.....8
R22-6V-10R13	SR12-14-3R15	TL-5-126	WC-B-SJ7	WWC-B-SJ8
R22-6V-22R13	SR12-3R.....15	TL-6-125	WC-G-14R7	WWC-G-25R8
R22-8V-10R13	SR16-3R.....15	TL-ADJ525	WC-G-25R7	WWC-G-6R8
R22-8V-22R13	SR22-3R.....15	TL-AWS26	WC-G-B7	WWC-G-B8
RCC-1-5050	SRPE-75047	TL-CCIH27	WC-G-C7	WWC-G-C.....8
RCC-2-3450	SS11100-10R.....41	TL-CRP27	WC-G-SJ7	WWC-G-SJ8
RCC-3-2550	SS12-10-3R.....15	TL-DC27	WC-O-12R7	WWC-GR-25R9
S12-8V-50R13	SS16-10-3R.....15	TL-ISS28	WC-O-25R7	WWC-GR-6R9
S12-8V-8R13	SS22-10-3R.....15	TL-LNP28	WC-O-B7	WWC-GR-B9
S16-6V-100R13	SS6100-10R.....41	TL-LP28	WC-O-C7	WWC-GR-C.....9
S16-6V-10R13	SWL-1QR23	TL-RCR26	WC-R-25R7	WWC-GR-SJ9
S16-6V-20R13	TB3096-10.....15	TL-WS625	WC-R-6R7	WWC-R-25R.....8
S16-8V-100R13	TB3096-6.....15	TRT-20041	WC-R-B7	WWC-R-6R.....8
S16-8V-10R13	TB3096-8.....15	TWHS-093-4-8R48	WC-R-C.....7	WWC-R-B.....8
S16-8V-20R13	TES-11133	TWHS-1000-4-2R ...48	WC-R-SJ7	WWC-R-C.....8
S22-4V-100R13	TES-12235	TWHS-125-4-7R48	WC-Y-25R.....7	WWC-R-SJ8
S22-4V-10R13	TES-13135	TWHS-187-4-8R48	WC-Y-9R.....7	WWC-T-25R8
S22-4V-20R13	TES-233	TWHS-250-4-6R48	WC-Y-B7	WWC-T-6R8
S22-8V-100R13	TES-AUTO35	TWHS-375-4-3R48	WC-Y-C.....7	WWC-T-B8
S22-8V-20R13	TES-BT36	TWHS-500-4-3R48	WC-Y-CJ.....7	WWC-T-C8
S22-8V-7R13	TES-CON.....35	TWHS-750-4-2R48	WMB-LC47	WWC-T-CJ8
SB12-3R.....15	TES-CT34	V1250-3R41	WPB-10R17	WWC-Y-25R8
SB1408S.....10	TES-DCM32	V850-5R41	WPI-10R17	WWC-Y-6R8
SB1408S-8R.....10	TES-DT1832	WAGS-4/0-448	WPW-10R17	WWC-Y-B8
SB16-3R.....15	TES-LVT33	WC-A-25R7	WWC-A-25R.....8	WWC-Y-C8
SB1810S.....10	TES-MT1231	WC-A-9R7	WWC-A-5R.....8	WWC-Y-CJ.....8
SB1810S-12R.....10	TES-MT1931	WC-AYR-160R.....7	WWC-AYR-160R.....8	

NOTES



ADDRESS
9730 Northcross Center Court
Huntersville, North Carolina
28078 USA



PHONE
800.321.5847



FAX
800.841.5566



EMAIL
nsi@nsiindustries.com



WEB
www.nsiindustries.com

