



SATCO

LIGHT BULBS





SATCO Corporate Headquarters, Brentwood, NY

Light Bulb Source Book–

We are pleased to present this latest edition of our Light Bulb Source Book. Many new lamps and accessories have been added. Each section is color coded and crafted to locate and identify a specific item in each category with ease.

Satco is committed to providing unsurpassed quality service and produce assortment. Many of our product categories are supported by self stocking merchandising systems and demonstration displays. These efforts, along with many others make Satco the preferred choice in light sources and electrical related products.

Our vast distribution network affords us the unique ability to have the products you want and need in stock and ready to ship from one of our state of the art facilities totaling nearly one million square feet!

Locations –

- ① Brentwood, New York
(Corporate Headquarters)
- ② Seattle, Washington
- ③ San Francisco, California
- ④ Dallas, Texas
- ⑤ Miami, Florida
- ⑥ Puerto Rico



The Complete Satco Product Line



The Light Bulb Source Book

An easy to use catalog sorted by lamp type.



The Lamp Specification Catalog

A technical guide to our lamp selection.



General Lighting Products

Featuring:

- OEM & Consumer Hardware
- Electrical Accessories
- Glassware
- Track & Lighting Fixtures
- Portable Lamps



Nuvo Lighting

Satco's Decorative Lighting Brand



NATIONAL TOLL-FREE
1-800-43-SATCO (1-800-437-2826)

NEW YORK EXECUTIVE OFFICES & WAREHOUSE:
110 Heartland Blvd.
Brentwood, N.Y. 11717
800-437-2826
(631) 243-2022
FAX:(631) 243-2027

TEXAS
2000 Valwood Parkway
Farmers Branch,
Texas 75234
800-437-2826
(972) 247-2437
FAX:(972) 247-5408

WASHINGTON
4710 116th St. S.W.
Mukilteo,
Washington 98275
800-437-2826
(425) 789-3300
FAX:(425) 789-3310

FLORIDA
900 N.W. 159th Drive
Miami, Florida 33169
800-437-2826
(305) 624-2044
FAX:(305) 623-0286

CALIFORNIA
31288 San Benito St.
Hayward, California 94544
800-437-2826
(510) 487-4822
FAX:(510) 487-8955

PUERTO RICO
Bldg 3, Compeche St. 22
Julio N. Matos Industrial Park
Bo Martin Gonzales
Carolina, PR 00984
800-437-2826
(787) 757-3510
FAX:(787) 757-3540

www.satco.com

the
SATCO
advantage

Six fully inventoried distribution centers.

Each Satco facility features the latest warehouse management systems ensuring that each order is addressed in a timely and efficient manner.

Comprehensive product selection we have what you need.

Our unique product offering positions us as a "One Shop" vendor. Satco has compiled a variety products through various industry relationships which makes us the primary choice for selection and service.

Products produced to the highest industry standards.

Quality products – An adage we've built our company by. Every item we sell has been designed, produced and tested to meet or exceed industry benchmarks for quality and testing. Quality assurance is controlled on all levels from production to shipping.

Innovative technology.

Satco owns numerous patents on lamp and lighting technology. As a leader we have introduced many new concepts that have been embraced by the lighting community.

Retail packaging and merchandising programs.

Satco's product assortment includes many retail point of purchase items packaged for the consumer market. These product programs are supported by eye-catching easy to use merchandisers

Forty years of performance.

A proven history of service, quality and relationships are the integral part of who we are. We value our long term associations and looking forward to many more successful years together.

Exceptional customer service.

The backbone of any company is their customer service. Each of our distribution centers are staffed with highly experienced knowledgeable personnel ready to assist. If you can't locate an item you are looking for, just ask – chances are we have it!

LAMPS

at a glance

Incandescent Lamps

Advantages

- Low initial cost
- Low fixture cost
- Simple installation
- Inexpensive to dim
- All-weather operation
- High CRI

Disadvantages

- Voltage sensitive
- Lowest efficacy
- Short life
- Heat

Tungsten Halogen

Advantages

- Whiter light than incandescent
- Excellent lumen maintenance
- Longer life than incandescent
- More efficient than incandescent

Disadvantages

- More costly than incandescent

Fluorescent Lamps

Advantages

- High efficacy
- Very good color
- Wide range of colors
- Good lumen maintenance
- Long life

Disadvantages

- Temperature effects
- Requires a ballast
- Light control

Mercury Vapor

Advantages

- Good for landscape lighting
- Long life
- All-weather operation

Disadvantages

- Lowest HID efficacy
- Poor lumen maintenance
- Poor color
- Requires a ballast
- Restrike time

High Pressure Sodium

Advantages

- Highest efficacy
- Long life
- Universal burning position
- Range of wattages
- Good lumen maintenance
- All-temperature operation

Disadvantages

- Color
- Requires a ballast
- Cycling (standard lamp)

Metal Halide

Advantages

- High efficacy
- Good color
- Good lumen maintenance
- Wide range of wattages
- Medium-long life
- All-temperature operation

Disadvantages

- Color shift
- Hot restrike time
- Requires a ballast

GLOSSARY

of terms

Ampere

A unit of measurement which expresses the rate of flow of electricity.

Average Rated Life

An average rating, in hours indicating when half of a large group of lamps have failed, when operated at rated lamp voltage and current.

Ballast

A device used with a discharge lamp to obtain the necessary voltage for starting and operating.

Center Beam Candlepower (CBCP)

The intensity of light produced at the center of a reflector lamp, expressed in candelas.

Color Rendering Index (CRI)

The measure of a light source to render color correctly.

Lamp

A manufactured light source. The three main categories are: incandescent, Fluorescent and HID (high intensity discharge).

Light

Radiant energy that is capable of producing a visual light.

Maximum Overall Length (MOL)

The total length of a lamp from the top of bulb to the bottom of the base.

Power Factor

A measure of the effectiveness with which a device converts volt-amperes to watts.

Total Harmonic Distortion (THD)


The rating which expresses the ability of a ballast not to affect the frequency.

Voltage

The measurement of electrical potential expressed in volts (V).

Reference Guide

Lamp Logic



Size: Incandescent bulb size is determined by the bulb's maximum diameter (the diameter at its widest part). This measurement is always expressed in eighths of an inch.

For example; an A19 bulb's maximum diameter is 19 eighths of an inch or 19/8" or 2 3/8".


A G40 bulb is 40 / 8" or 5".

Following are some examples of popular bulb shapes.


Bulb Shapes

The size and shape of a bulb is designated by a letter code followed by a number. The letter indicates the shape of the bulb and the number indicates the diameter in eighths of an inch.


Incandescent Bulb Shapes



Miniature Lamps




Base Types




Reference Guide

product reference guide


HID Bulb Shapes



Compact Fluorescent Bulb Shapes



Compact Fluorescent Bases



| Color Temp. | Warm | Neutral | Cool | Daylight |
|----------------|---------------------|-----------------------------|--------------------|-----------------------------|
| Kelvin Range | 3000K | 3500K | 4100K | 5000K |
| Effect & Moods | Warm & Friendly | Inviting & Comfortable | Clean & Organized | Bright & Alert |
| Application | Homes & Restaurants | Showrooms & Reception Areas | Office & Hospitals | Galleries & Jewelry Display |



Color Application Guide

Color Rendering

Lamp Color



The Color Rendering Index is based on a maximum rating of 100. Light sources with a low CRI will make objects appear washed out and dull. Lamps with high CRI ratings will be more vivid and bring life to the subject.

The color of light is based on a color temperature scale which is rated in Kelvins. A warm color of light would be in 2000 - 3000K range and would make the red, orange and yellow colors more predominant. Light sources with a color temperature in the 4000K range would feature more blue or cool colors. The photographs shown here illustrate how the color of a light source can impact the appearance of objects.

Color Matching

Choose from a wide assortment of color temperatures to match different lamp types in an application.

Many of the light sources shown throughout the catalog offer a wide range of color options to suit your specific design needs.

Fluorescent Bulb Shapes




Table of Contents



table of contents

REFLECTORS




Reflectors

| | |
|------------------------|-------|
| R14 & R16 | 14 |
| K19 | 21 |
| R20 & BR25 | 15 |
| BR30 | 16-18 |
| BR40 | 19 |
| ER30 & ER40 | 25 |
| R20/BR30/BR40 Halogen | 20 |
| Plant Light Reflectors | 24 |
| BR38 Floods | 25 |




Color Reflectors

| | |
|-------------|----|
| R20 Colors | 22 |
| BR30 Colors | 23 |
| BR38 Colors | 27 |



PAR Reflectors

| | |
|---------------------|-------|
| Incandescent PARs | 29-30 |
| Soft Ray PARs | 31 |
| PAR14-PAR38 Halogen | 32-36 |



Heat Lamps

| | |
|-----------|----|
| BR38 Red | 28 |
| R40 Clear | 28 |
| R40 Red | 28 |

DECORATIVE INCANDESCENT LAMPS



Globe Lights

| | |
|--------------------------|-------|
| G8 & G12 Globe Lights | 40 |
| G12 Colored Globe Lights | 41 |
| G16½ Silver Crown | 41 |
| G16½ Globe Lights | 42-43 |
| G14 & G17 Globe Lights | 44 |
| G16½ & G18½ Med. | 45 |
| G25 Globe Lights | 46-49 |
| G25 Silver Crown | 50 |
| G40 Globe Lights | 51 |



Decorative Bulbs

| | |
|---------------------------|-------|
| Chandelier Bulbs 120V | 52-56 |
| Chandelier Bulbs 130V | 57-61 |
| Petite & Specialty | 62-63 |
| F10 & F15 Flame | 64 |
| Krypton G16½, Torp. Flame | 65 |
| Satco-Escent® | 66-67 |
| Flicker Bulbs | 68 |
| Prismatics Bulbs | 69 |
| Colored Torpedo | 70 |

GENERAL SERVICE LAMPS



| | |
|--------------------------------|-------|
| Night Light Bulbs | 74 |
| Display/Sign Bulbs | 75 |
| Tubular | 76-78 |
| Hi-Intensity | 79 |
| Appliance/Indicators | 80-81 |
| A15 | 82-83 |
| A19 2 Pack | 84-85 |
| A19 4 Pack | 86 |
| A19 Black Light/Bug/Silver Cr. | 88 |
| A19 Party Bulbs | 89-91 |



| | |
|------------------------------|---------|
| A19 EconoBrite™ | 92-93 |
| A19 Energy Saver | 102 |
| A19/A21/A23 Commercial Serv. | 87 |
| A19 Safety Coated | 94 |
| A21 Safety Coated | 95 |
| A19 Rough Service | 95 |
| 3-Way | 96-97 |
| A21 Household | 98 |
| A23 Household | 99 |
| PS25/PS35 | 100-101 |

Table of Contents

SPECIALTY LAMPS



Linear Incandescent106
Neodymium Lamps107-109
Shatter-Proof110-111
A19 Low Voltage112



Export A19 130V-230V113
Export G25 220V114
Export Decorative 220V115
Export Reflectors 230V114

HALOGEN LAMPS



PAR14~PAR38 Halogen ..120-124
Soft Ray PARs125
R20/BR30/BR40 Halogen126
MR8/MR11 12V & 24V127
MR16 120V128
MR16 12V & 24V129-131
ALR132
AR70/AR111133
PAR36/PAR 56/PAR64134



General Service135
JD Bayonet136
JD Mini-Can137
JD Euro137
T3 Krypton/Xenon138
Capsules 12V/24V/120V139
J-Type140
Ball Lite141
A-Type142

CARDED LAMPS



Chandelier Bulbs 120V ..146-151
Chandelier Bulbs 130V ..152-156
Globe157-159
Satco-Escent®160
F10 & F15 Flame161-162
Krypton/Diamond Cut163
Silicone Tip163
Ceiling Fan Bulbs164
Prismatic Bulbs165
Flicker Bulbs166



Tubular167
Hi-Intensity/Sign168
R14 &R16 Reflectors171
MR11 & MR16172
JD E11/E14/BA15D173
Capsules 12V/120V174
GU10/JDR175
Double Envelope175
J Type176-177
Compact Fluorescent178

FLUORESCENT LAMPS



T2-T8 Linear Tubes182-188
T8 U Bend Tubes189
T12 Linear Tubes190-192
T12 U Bend Tubes193
T6/T8/T12 Slimline Tubes .194-195
T12 HO/VHO Tubes196-197
T5/T9 Circline Tubes198-199
Shatterproof Lamps200-201
Pin Based Compact202-213



Self Ballasted

Mini Spiral CFL214
Standard Spiral CFL215
R20~R40/BR38 CFL216
A Type CFL219
Torpedo/Bullet/Globe CFL220
Spiral w/Photocell CFL221
Bug CFL221
Circline222

Table of *Contents*



table of contents

HID LAMPS



Metal Halide

Mogul Base . . .226-229,232-233
 Medium Base226-229
 PAR Type230
 R40 Reflector230
 Double Ended231
 Single Ended T Type231
 Double Ended T Type231



Mercury Vapor

Mogul Base234-235
 Medium Base235
High Pressure Sodium
 Medium Base236
 Mogul Base237-239
Low Pressure Sodium
 Sox Lamps240

SEALED BEAM LAMPS



Screw Terminal

PAR36244
 PAR46245



Mogul End Prong

PAR56.246
 PAR64.246

MINIATURE & SPECIALTY LAMPS



Incandescent

B-3½, G-3½, G-4½252
 G-6, B-6, T-5253
 S-8, RP11254



Xenon

T-3¼, T5 Wedge255
 T-3¼ Double End Cap256
 RLX256

BALLASTS & ACCESSORIES



Ballasts

Electronic260-262
 Magnetic263-264
 Socket Ballasts265



Accessories

Bulb Changers266
 Bulb Cages266
 Bulb Extenders266

R14 & R16

1500 Hours



R14
Intermediate Base
120 Volt
S3205 25 Watt
S3215 40 Watt



R14
E14/Euro. (Mignon) Base
130 Volt
S3396 40 Watt

Not Shown Actual Size



R16
Medium Base
120 Volt
S3214 40 Watt



Shortneck R14
Medium Base
120 Volt
S3601 25 Watt
S3602 40 Watt



R14
Medium Base
120 Volt
S3604 25 Watt
S3605 40 Watt

Packing:
Individually Boxed
500/Master, 25/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|----------|-----------------|-----------|-----------|-------|------------------|--------|----------|---------|------------|----------------------|
| 25 | R14 | Int. | S3205 | 25R14N | Lt. Frost | 120V | 1500 | 135 | CC2V | 2 5/8" | Box | 500/25 |
| 25 | R14 | Med. | S3601 | 25R14 | Lt. Frost | 120V | 1500 | 135 | CC2V | 2 1/4" | Box | 500/25 |
| 25 | R14 | Med. | S3604 | 25R14 | Lt. Frost | 120V | 1500 | 135 | CC2V | 2 5/8" | Box | 500/25 |
| 40 | R14 | E14/Euro | S3396 | 40R14 | Lt. Frost | 130V | 1500 | 280 | CC2V | 2 5/8" | Box | 500/25 |
| 40 | R14 | Int. | S3215 | 40R14N | Lt. Frost | 120V | 1500 | 280 | CC2V | 2 5/8" | Box | 500/25 |
| 40 | R14 | Med. | S3602 | 40R14 | Lt. Frost | 120V | 1500 | 280 | CC2V | 2 1/4" | Box | 500/25 |
| 40 | R14 | Med. | S3605 | 40R14 | Lt. Frost | 120V | 1500 | 280 | CC2V | 2 5/8" | Box | 500/25 |
| 40 | R16 | Med. | S3214 | 40R16 | Frost | 120V | 1500 | 280 | C-9 | 3 7/16" | Box | 500/25 |

R20 & BR25

2000 Hours

Not Shown Actual Size

R20

Medium Base

120 Volt

S3210 30 Watt

S3204 50 Watt

S3211 75 Watt

S3226 100 Watt

S2810 30 Watt/130 Volt

S3804 50 Watt/130 Volt

S2811 75 Watt/130 Volt

Packing:

Individually Sleeved

96/Master

12/Inner



BR25

Medium Base

120 Volt

S2806 65 Watt

S2807 85 Watt

Packing:

Individually Sleeved

96/Master

12/Inner



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 30 | R20 | Med. | S3210 | 30R20 | Frost | 120V | 2000 | 185 | CC-9 | 4" | Sleeve | 96/12 |
| 30 | R20 | Med. | S2810 | 30R20/130 | Frost | 130V | 2000 | 185 | CC-9 | 4" | Sleeve | 96/12 |
| 50 | R20 | Med. | S3204 | 50R20 | Frost | 120V | 2000 | 375 | CC-9 | 4" | Sleeve | 96/12 |
| 50 | R20 | Med. | S3804 | 50R20/130 | Frost | 130V | 2000 | 375 | CC-9 | 4" | Sleeve | 96/12 |
| 75 | R20 | Med. | S3211 | 75R20 | Frost | 120V | 2000 | 690 | CC-9 | 4" | Sleeve | 96/12 |
| 75 | R20 | Med. | S2811 | 75R20/130 | Frost | 130V | 2000 | 690 | CC-9 | 4" | Sleeve | 96/12 |
| 100 | R20 | Med. | S3226 | 100R20 | Frost | 120V | 2000 | 925 | CC-9 | 4" | Sleeve | 96/12 |
| 65 | BR25 | Med. | S2806 | 65BR25/FL | Frost | 120V | 2000 | 600 | CC-6 | 4 3/4" | Sleeve | 96/12 |
| 85 | BR25 | Med. | S2807 | 85BR25/FL | Frost | 120V | 2000 | 800 | CC-6 | 4 3/4" | Sleeve | 96/12 |

BR30

2000 Hours

Not Shown Actual Size

BR30

Medium Base

S3259 50 Watt

S2808 65 Watt

S3408 65 Watt/130 Volt

S2809 85 Watt

S3409 85 Watt/130 Volt

Packing: Individually Sleeved
96/Master, 12/Inner



Colorful
Multi Pack
Inner Cartons

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack Type | Mst.Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|-----------|----------------------|
| 50 | BR30 | Med. | S3259 | 50BR30/FL | Frost | 120V | 2000 | 550 | CC-9 | 5 3/8" | Sleeve | 96/12 |
| 65 | BR30 | Med. | S2808 | 65BR30/FL | Frost | 120V | 2000 | 685 | CC-9 | 5 3/8" | Sleeve | 96/12 |
| 65 | BR30 | Med. | S3408 | 65BR30/FL | Frost | 130V | 2000 | 685 | CC-9 | 5 3/8" | Sleeve | 96/12 |
| 85 | BR30 | Med. | S2809 | 85BR30/FL | Frost | 120V | 2000 | 925 | CC-9 | 5 3/8" | Sleeve | 96/12 |
| 85 | BR30 | Med. | S3409 | 85BR30/FL | Frost | 130V | 2000 | 925 | CC-9 | 5 3/8" | Sleeve | 96/12 |

2000 Hours

2 Pack **BR30**



Not Shown Actual Size

BR30/2 Pack

Medium Base

S2817 65 Watt

S3417 65 Watt/130 Volt

Packing: 2/Box

60 2-Packs /Master

Sold Per Pack

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn. |
|-------|-----------|------|-----------------|---------------|--------|-------|------------------|--------|----------|--------|------------|----------|
| 65 | BR30 | Med. | S2817 | 65BR30/FL/2PK | Frost | 120V | 2000 | 685 | CC-9 | 5 3/8" | Box/2 | 60/2 |
| 65 | BR30 | Med. | S3417 | 65BR30/FL/2PK | Frost | 130V | 2000 | 685 | CC-9 | 5 3/8" | Box/2 | 60/2 |

BR30

5000 Hours

BR30
 Long Life
 Commercial Grade

Medium Base
 130 Volt

S6208 65 Watt/130 Volt
 Packing: Individually Sleeved
 24/Master



Not Shown Actual Size


| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|--------------|--------|-------|------------------|--------|----------|--------|------------|-----------|
| 65 | BR30 | Med. | S6208 | 65BR30/FL/LL | Frost | 130V | 5000 | 532 | CC-9 | 5 3/8" | Sleeve | 24 |

2500 Hours

Not Shown Actual Size



LONGER LIFE!



BR40

Medium Base

S2853 65 Watt

S4453 65 Watt/130 Volt

S2854 85 Watt/120-130 Volt

S2855 120 Watt

S4455 120 Watt/130 Volt

*Packing: Individually Sleeved
24/Master*

reflectors

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated | | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn. |
|-------|-----------|------|-----------------|-----------|--------|------------|-------|--------|----------|--------|------------|----------|
| | | | | | | Volts | Hours | | | | | |
| 65 | BR40 | Med. | S2853 | 65BR/FL | Frost | 120V | 2500 | 685 | CC-6 | 6 1/2" | Sleeve | 24 |
| 65 | BR40 | Med. | S4453 | 65BR/FL | Frost | 130V | 2500 | 685 | CC-6 | 6 1/2" | Sleeve | 24 |
| 85 | BR40 | Med. | S2854 | 85BR/FL | Frost | 120-130V | 2500 | 925 | CC-6 | 6 1/2" | Sleeve | 24 |
| 120 | BR40 | Med. | S2855 | 120BR/FL | Frost | 120V | 2500 | 1150 | CC-6 | 6 1/2" | Sleeve | 24 |
| 120 | BR40 | Med. | S4455 | 120BR/FL | Frost | 130V | 2500 | 1150 | CC-6 | 6 1/2" | Sleeve | 24 |

Halogen Reflectors



R20/BR30/BR40

2500 Hours

- Nickel Plated Brass Base
- High Lumen Output
- Brilliant White Light
- Better Color Rendering than Standard Floods
- 20% Brighter & Longer Lasting



reflectors

R20

Medium Base
120 Volt
S4500 50 Watt
Packing: Individually Sleeved
48/Master, 6/Inner

BR30

Medium Base
120 Volt/130Volt
S4501 60 Watt
S4401 60 Watt/130 Volt
S4502 75 Watt
S4402 75 Watt/130 Volt
Packing: Individually Sleeved
48/Master, 6/Inner

BR40

Medium Base
120 Volt
S4504 75 Watt
S4503 100 Watt
Packing: Individually Sleeved
24/Master, 6/Inner

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Lumens | Kelvin | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|----------------|------|-------|------------------|--------|--------|--------|------------|-----------------------|
| 50 | R20 | Med. | S4500 | 50R20/FL/HAL | 70° | 120V | 2500 | 480 | 3000K | 4" | Sleeve | 48/6 |
| 60 | BR30 | Med. | S4501 | 60BR30/FL/HAL | 80° | 120V | 2500 | 730 | 3000K | 5 3/8" | Sleeve | 48/6 |
| 60 | BR30 | Med. | S4401 | 60BR30/FL/HAL | 80° | 130V | 2500 | 730 | 3000K | 5 3/8" | Sleeve | 48/6 |
| 75 | BR30 | Med. | S4502 | 75BR30/FL/HAL | 80° | 120V | 2500 | 900 | 3000K | 5 3/8" | Sleeve | 48/6 |
| 75 | BR30 | Med. | S4402 | 75BR30/FL/HAL | 80° | 130V | 2500 | 900 | 3000K | 5 3/8" | Sleeve | 48/6 |
| 75 | BR40 | Med. | S4504 | 75BR40/FL/HAL | 90° | 120V | 2500 | 900 | 3000K | 6 1/2" | Sleeve | 24/6 |
| 100 | BR40 | Med. | S4503 | 100BR40/FL/HAL | 90° | 120V | 2500 | 1400 | 3000K | 6 1/2" | Sleeve | 24/6 |

1500 Hours

2 Pack **K19**



Satco **K19** directional reflector lamps are specifically designed to create a soft, glare free light source.

Not Shown Actual Size

Directional Reflectors

White

*Medium Base
120 Volt*

S4976 40 Watt

S4977 60 Watt

S4978 75 Watt

S4979 100 Watt

Packing: 2/Box, 12/2 Packs

Sold Per Pack

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn. |
|-------|-----------|------|-----------------|------------|--------|-------|------------------|--------|----------|--------|------------|----------|
| 40 | K19 | Med. | S4976 | 40K19/2PK | White | 120 | 1500 | 260 | C-9 | 4 1/8" | Box/2 | 12 |
| 60 | K19 | Med. | S4977 | 60K19/2PK | White | 120 | 1500 | 520 | C-9 | 4 1/8" | Box/2 | 12 |
| 75 | K19 | Med. | S4978 | 75K19/2PK | White | 120 | 1500 | 680 | C-9 | 4 1/8" | Box/2 | 12 |
| 100 | K19 | Med. | S4979 | 100K19/2PK | White | 120 | 1500 | 1000 | C-9 | 4 1/8" | Box/2 | 12 |

reflectors

Reflectors *Brass Base*



R20 colors

130 Volt 2000 Hours

Not Shown Actual Size

Medium Base 130 Volt
Packing: Individually Sleeved
96/Master, 12/Inner



S3200 50 Watt Red



S3201 50 Watt Green



S3202 50 Watt Blue



S3203 50 Watt Amber



S3212 50 Watt Pink

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 50 | R20 | Med. | S3200 | 50R20/R | Red | 130 | 2000 | n/a | C-9 | 4" | Sleeve | 96/12 |
| 50 | R20 | Med. | S3201 | 50R20/G | Green | 130 | 2000 | n/a | C-9 | 4" | Sleeve | 96/12 |
| 50 | R20 | Med. | S3202 | 50R20/B | Blue | 130 | 2000 | n/a | C-9 | 4" | Sleeve | 96/12 |
| 50 | R20 | Med. | S3203 | 50R20/A | Amber | 130 | 2000 | n/a | C-9 | 4" | Sleeve | 96/12 |
| 50 | R20 | Med. | S3212 | 50R20/PK | Pink | 130 | 2000 | n/a | C-9 | 4" | Sleeve | 96/12 |

reflectors

2000 Hours 130 Volt

BR30 colors



S3227 75 Watt Green



S3240 75 Watt Red

Not Shown Actual Size

*Medium Base 130 Volt
Packing: Individually Sleeved
96/Master, 12/Inner*



S3213 75 Watt Pink



S3239 75 Watt Amber



S3228 75 Watt Blue

reflectors

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|----------------------|
| 75 | BR30 | Med. | S3240 | 75BR30/R | Red | 130 | 2000 | n/a | C-9 | 5 3/8" | Sleeve | 96/12 |
| 75 | BR30 | Med. | S3227 | 75BR30/G | Green | 130 | 2000 | n/a | C-9 | 5 3/8" | Sleeve | 96/12 |
| 75 | BR30 | Med. | S3228 | 75BR30/B | Blue | 130 | 2000 | n/a | C-9 | 5 3/8" | Sleeve | 96/12 |
| 75 | BR30 | Med. | S3239 | 75BR30/A | Amber | 130 | 2000 | n/a | C-9 | 5 3/8" | Sleeve | 96/12 |
| 75 | BR30 | Med. | S3213 | 75BR30/PK | Pink | 130 | 2000 | n/a | C-9 | 5 3/8" | Sleeve | 96/12 |

Plant Light *Brass Base*



Reflectors

120 Volt / 2000 Hours

Not Shown Actual Size



R20/R25/R30

Plant Lights

Medium Base

120 Volt

S2850 50 Watt/R20

S2851 75 Watt/R25

S2852 150 Watt/R30

Packing: Individually Boxed
96/Master, 12/Inner



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|--------------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 50 | R20 | Med. | S2850 | 50R20/Plant | 120V | 2000 | n/a | C-9 | 4" | Box | 96/12 |
| 75 | R25 | Med. | S2851 | 75R25/Plant | 120V | 2000 | n/a | C-9 | 4 3/4" | Box | 96/12 |
| 150 | R30 | Med. | S2852 | 150R30/Plant | 120V | 2000 | n/a | C-9 | 5 3/8" | Box | 96/12 |

reflectors

2000 Hours

ER30 & ER40

Elliptical Reflectors produce more useable light beyond the lamp surface. They are perfect for use in deeply recessed fixtures.



ER30

Elliptical

Medium Base

130 Volt

S4956 50 Watt

S4957 75 Watt

Packing:

Individually Sleeved
24/Case

ER40

Elliptical

Medium Base

130 Volt

S4958 120 Watt

Packing:

Individually Sleeved
24/Case

Not Shown

Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------|
| 50 | ER30 | Med. | S4956 | 50ER30 | Frost | 130V | 2000 | 310 | CC6 | 6 1/8" | Sleeve | 24 |
| 75 | ER30 | Med. | S4957 | 75ER30 | Frost | 130V | 2000 | 620 | CC6 | 6 1/8" | Sleeve | 24 |
| 120 | ER40 | Med. | S4958 | 120ER40 | Frost | 130V | 2000 | 1180 | CC6 | 7 1/4" | Sleeve | 24 |

Reflectors *Brass Base*



BR38 Weatherproof

2000 Hours

BR38 Medium Base
120 Volt /130 Volt

S4420 75 Watt

S4430 75 Watt/130 Volt

S4421 150 Watt

S4431 150 Watt/130 Volt

Packing: Individually Boxed
12/Master

S4422 75 Watt (2 Pack)

S4423 150 Watt (2 Pack)

Packing: 2 per Box

8 2pk/Master

Sold Per Pack



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn. |
|-------|-----------|------|-----------------|----------------|--------|-------|------------------|--------|----------|---------|------------|----------|
| 75 | BR38 | Med. | S4420 | 75BR38/FL | Clear | 120V | 2000 | 700 | CC9 | 5 5/16" | Box | 12 |
| 75 | BR38 | Med. | S4430 | 75BR38/FL | Clear | 130V | 2000 | 700 | CC9 | 5 5/16" | Box | 12 |
| 75 | BR38 | Med. | S4422 | 75BR38/FL/2PK | Clear | 120V | 2000 | 700 | CC9 | 5 5/16" | Box/2 | 8 |
| 150 | BR38 | Med. | S4421 | 150BR38/FL | Clear | 120V | 2000 | 1550 | CC9 | 5 5/16" | Box | 12 |
| 150 | BR38 | Med. | S4431 | 150BR38/FL | Clear | 130V | 2000 | 1550 | CC9 | 5 5/16" | Box | 12 |
| 150 | BR38 | Med. | S4423 | 150BR38/FL/2PK | Clear | 120V | 2000 | 1550 | CC9 | 5 5/16" | Box/2 | 8 |

2000 Hours

BR38 Weatherproof



S4424 100 Watt Red



S4425 100 Watt Amber

BR38
Colors

Medium Base
120 Volt
Packing:
Individually Boxed
6/Master



S4426 100 Watt Yellow



S4427 100 Watt Green



S4428 100 Watt Blue



S4429 100 Watt Pink

Not Shown
Actual Size

reflectors

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|------------|--------|-------|------------------|--------|----------|---------|------------|-----------|
| 100 | BR38 | Med. | S4424 | 100BR38/R | Red | 120V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | Med. | S4425 | 100BR38/A | Amber | 120V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | Med. | S4426 | 100BR38/Y | Yellow | 120V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | Med. | S4427 | 100BR38/G | Green | 120V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | Med. | S4428 | 100BR38/B | Blue | 120V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | Med. | S4429 | 100BR38/PK | Pink | 120V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |

Heat lamps

5000 Hours



R40/Clear
Infrared Heat Lamp
Medium Base (120 Volt)
S4999 250 Watt Clear

Packing: Individually Sleeved, 12/Master



R40/Red
Infrared Heat Lamp
Medium Base (120 Volt)
S4998 250 Watt Red

Packing: Individually Sleeved, 12/Master



BR38/Red
Infrared Heat Lamp
Medium Base (120 Volt)
S4751 175 Watt Red

Packing: Individually Boxed, 12/Master



R40/Clear
Infrared Heat Lamp
Medium Base (120 Volt)
S4750 125 Watt Clear

Packing: Individually Boxed, 12/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|------------|--------|-------|------------------|--------|----------|---------|------------|-----------|
| 125 | R40 | Med. | S4750 | 125R40/1 | Clear | 120V | 5000 | n/a | C-9 | 6 1/2" | Box | 12 |
| 175 | BR38 | Med. | S4751 | 175BR38/HR | Red | 120V | 5000 | n/a | C-9 | 5 5/16" | Box | 12 |
| 250 | R40 | Med. | S4999 | 250R40/1 | Clear | 120V | 5000 | n/a | C-9 | 6 1/2" | Sleeve | 12 |
| 250 | R40 | Med. | S4998 | 250R40/HR | Red | 120V | 5000 | n/a | C-9 | 6 1/2" | Sleeve | 12 |

Brass Base Reflectors

PAR38

2 Piece Construction

Weatherproof



Shown Actual Size

PAR38

Medium Base,
2 Piece Construction

S4952 65 Watt Flood

S4953 65 Watt Flood/130 Volt

S4951 65 Watt Spot

S4954 150 Watt Flood/130 Volt

S4955 150 Watt Spot/130 Volt

Packing: Individually Boxed
15/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Lumens | CBCP | Filament | M.O.L. | Pack. Type | Mst.Ctn. |
|-------|-----------|-----------|-----------------|---------------|-----------|-------|------------------|--------|-------|----------|---------|------------|----------|
| 65 | PAR38 | Med. Skt. | S4952 | 65PAR/FL | Flood 30° | 120V | 1750 | 715 | 1700 | CC-6 | 5 5/16" | Box | 15 |
| 65 | PAR38 | Med. Skt. | S4953 | 65PAR/FL/130 | Flood 30° | 130V | 1750 | 715 | 1700 | CC-6 | 5 5/16" | Box | 15 |
| 65 | PAR38 | Med. Skt. | S4951 | 65PAR/SP | Spot 12° | 120V | 1750 | 715 | 5500 | CC-6 | 5 5/16" | Box | 15 |
| 150 | PAR38 | Med. Skt. | S4954 | 150PAR/FL/130 | Flood 30° | 130V | 750 | 2175 | 4500 | CC-6 | 5 5/16" | Box | 15 |
| 150 | PAR38 | Med. Skt. | S4955 | 150PAR/SP/130 | Spot 12° | 130V | 750 | 2175 | 18000 | CC-6 | 5 5/16" | Box | 15 |

130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE

| | | | | | | | | | | | | | |
|-----|-------|-----------|--------------|---------------|-----------|------|------|------|-------|------|---------|-----|----|
| 57 | PAR38 | Med. Skt. | S4953 | 65PAR/FL/130 | Flood 30° | 130V | 4375 | 540 | 1285 | CC-6 | 5 5/16" | Box | 15 |
| 132 | PAR38 | Med. Skt. | S4954 | 150PAR/FL/130 | Flood 30° | 130V | 1875 | 1660 | 3435 | CC-6 | 5 5/16" | Box | 15 |
| 132 | PAR38 | Med. Skt. | S4955 | 150PAR/SP/130 | Spot 12° | 130V | 1875 | 1660 | 13735 | CC-6 | 5 5/16" | Box | 15 |

PAR Reflectors

PAR36/PAR38/PAR56

Not Shown Actual Size



PAR38 Side Prong

2 Piece Construction

Side Prong Base,

S4800 75 Watt Flood

S4801 75 Watt Spot

S4675* 90 Watt Halogen Flood

S4674* 90 Watt Halogen Spot

S4802 150 Watt Flood

S4803 150 Watt Spot

Packing: Individually Boxed

12/Master

*15/Master



PAR36 12 Volt Screw Terminal

INCANDESCENT

S4804 50 Watt PAR36 Wide Flood

S4805 50 Watt PAR36 Narrow Spot

HALOGEN

S4809 36 Watt PAR36 Wide Flood

S4808 36 Watt PAR36 Narrow Spot

S4807 36 Watt PAR36 Very Narrow Spot

S4806 50 Watt PAR36 Narrow Spot

Packing: Individually Boxed

12/Master

PAR56 120 Volt Mogul Side Prong

INCANDESCENT

S4810 300 Watt PAR56 Medium Flood

S4811 300 Watt PAR56 Wide Flood

S4963 300 Watt PAR56 Narrow Spot

Packing: Individually Boxed

12/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn. |
|-------|-----------|---------------|-----------------|------------------|-----------|-------|------------------|-------|--------|----------|---------|------------|----------|
| 75 | PAR38 | Side Prong | S4800 | 75PAR/3FL/MINE | Flood 30° | 120V | 2000 | 1750 | 765 | CC-6 | 4 5/16" | Box | 12 |
| 75 | PAR38 | Side Prong | S4801 | 75PAR/3SP/MINE | Spot 15° | 120V | 2000 | 5900 | 765 | CC-6 | 4 5/16" | Box | 12 |
| 90 | PAR38 | Side Prong | S4675 | 90PAR/CAP/3FL | Flood 30° | 120V | 2500 | 3500 | 1310 | CC-8 | 4 5/16" | Box | 15 |
| 90 | PAR38 | Side Prong | S4674 | 90PAR/CAP/3SP | Spot 12° | 120V | 2500 | 14300 | 1310 | CC-8 | 4 5/16" | Box | 15 |
| 150 | PAR38 | Side Prong | S4802 | 150PAR/3FL/MINE | Flood 30° | 120V | 2000 | 3600 | 1740 | CC-6 | 4 5/16" | Box | 12 |
| 150 | PAR38 | Side Prong | S4803 | 150PAR/3SP/MINE | Spot 18° | 120V | 2000 | 9200 | 1740 | CC-6 | 4 5/16" | Box | 12 |
| 50 | PAR36 | Screw Term. | S4804 | 50PAR36/WFL | Flood 35° | 12V | 2000 | 720 | 330 | C-6 | 2 3/4" | Box | 12 |
| 50 | PAR36 | Screw Term. | S4805 | 50PAR36/NSP | Spot 8° | 12V | 2000 | 11000 | 330 | C-6 | 2 3/4" | Box | 12 |
| 36 | PAR36 | Screw Term. | S4809 | 36PAR36/CAP/WFL | Flood 32° | 12V | 4000 | 1000 | 500 | C-8 | 2 3/4" | Box | 12 |
| 36 | PAR36 | Screw Term. | S4808 | 36PAR36/CAP/NSP | Spot 13° | 12V | 4000 | 3500 | 500 | C-8 | 2 3/4" | Box | 12 |
| 36 | PAR36 | Screw Term. | S4807 | 36PAR36/CAP/VNSP | Spot 5° | 12V | 4000 | 17000 | 500 | C-8 | 2 3/4" | Box | 12 |
| 50 | PAR36 | Screw Term. | S4806 | 50PAR36/CAP/NSP6 | Spot 6° | 12V | 4000 | 25000 | 700 | C-8 | 2 3/4" | Box | 12 |
| 300 | PAR56 | Mog End Prong | S4810 | 300PAR56/MFL | Flood 23° | 120V | 2000 | 24000 | 3840 | CC-13 | 5" | Box | 12 |
| 300 | PAR56 | Mog End Prong | S4811 | 300PAR56/WFL | Flood 37° | 120V | 2000 | 11000 | 3840 | CC-13 | 5" | Box | 12 |
| 300 | PAR36 | Mog End Prong | S4963 | 300PAR56/NSP | Spot 10° | 120V | 2000 | 68000 | 3840 | CC-13 | 5" | Box | 12 |

Not Shown Actual Size

PAR16/PAR20/PAR30/PAR38

Frosted Halogen Lamps

S O F T - R A Y

Introducing - Soft Ray, a new concept in halogen lighting. Our new line of frosted MR16 and PAR lamps offer a simple, cost effective solution to problems normally associated with standard halogen reflectors.

It is known that many users of traditional MR16 & PAR lamps object to the "headlamp look" or glare appearance of these lamps. Soft Ray lamps solve these problems and more!

- Glare Free
- Does not create hot spots
- Eliminates shadows & striations
- Produces a smooth and even beam pattern



PAR16



PAR20



PAR30 Short Neck



PAR30 Long Neck



PAR38

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|-----------|-----------------|---------------------|-----------|-------|------------------|--------|----------|---------|------------|-----------|
| 60 | PAR16 | Med. | S4108 | 60PAR16/FL/FROST | Flood 38° | 120V | 2500 | 525 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S4109 | 75PAR16/FL/FROST | Flood 38° | 120V | 2500 | 725 | CC-8 | 3 3/16" | Box | 15 |
| 50 | PAR20 | Med. | S4100 | 50PAR20/NFL/FROST | Flood 38° | 120V | 2500 | 450 | CC-8 | 3 3/8" | Box | 15 |
| 50 | PAR20 | Med. | S4200 | 50PAR20/NFL/FROST | Flood 38° | 130V | 2500 | 450 | CC-8 | 3 3/8" | Box | 15 |
| 50 | PAR30 | Med. | S4101 | 50PAR30/FL/FROST | Flood 38° | 120V | 2500 | 520 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4201 | 50PAR30/FL/FROST | Flood 38° | 130V | 2500 | 520 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4102 | 75PAR30/FL/FROST | Flood 38° | 120V | 2500 | 900 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4202 | 75PAR30/FL/FROST | Flood 38° | 130V | 2500 | 900 | CC-8 | 5 5/16" | Box | 15 |
| 50 | PAR30/LN | Med. | S4103 | 50PAR30/LN/FL/FROST | Flood 38° | 120V | 2500 | 520 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S4203 | 50PAR30/LN/FL/FROST | Flood 38° | 130V | 2500 | 520 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S4104 | 75PAR30/LN/FL/FROST | Flood 38° | 120V | 2500 | 900 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S4204 | 75PAR30/LN/FL/FROST | Flood 38° | 130V | 2500 | 900 | CC-8 | 4 1/2" | Box | 15 |
| 45 | PAR38 | Med. Skt. | S4105 | 45PAR38/FL/FROST | Flood 38° | 120V | 2500 | 450 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. Skt. | S4205 | 45PAR38/FL/FROST | Flood 38° | 130V | 2500 | 450 | CC-8 | 5 5/16" | Box | 15 |
| 60 | PAR38 | Med. Skt. | S4106 | 60PAR38/FL/FROST | Flood 38° | 120V | 2500 | 600 | CC-8 | 5 5/16" | Box | 15 |
| 60 | PAR38 | Med. Skt. | S4206 | 60PAR38/FL/FROST | Flood 38° | 130V | 2500 | 600 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4107 | 90PAR38/FL/FROST | Flood 38° | 120V | 2500 | 1150 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4207 | 90PAR38/FL/FROST | Flood 38° | 130V | 2500 | 1150 | CC-8 | 5 5/16" | Box | 15 |

PAR16/PAR20/PAR30

Whiter light, brighter colors, precise beam control.

Not Shown Actual Size



PAR16

PAR20

PAR30

SATCO PAR HALOGEN LAMPS QUALITY • VALUE • PERFORMANCE

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated | | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------------|---------|-------|------------|-------|--------|----------|---------|------------|-----------|
| | | | | | | | Hours | CBCP | | | | | |
| 45 | PAR16 | Med. | S2200 | 45PAR16/HAL/NFL | NFL 30° | 120V | 2500 | 1200 | 420 | CC-8 | 3 3/16" | Box | 15 |
| 45 | PAR16 | Med. | S2300 | 45PAR16/HAL/NFL | NFL 30° | 130V | 2500 | 1200 | 420 | CC-8 | 3 3/16" | Box | 15 |
| 60 | PAR16 | Med. | S2201 | 60PAR16/HAL/NFL | NFL 30° | 120V | 2500 | 1400 | 600 | CC-8 | 3 3/16" | Box | 15 |
| 60 | PAR16 | Med. | S2301 | 60PAR16/HAL/NFL | NFL 30° | 130V | 2500 | 1400 | 600 | CC-8 | 3 3/16" | Box | 15 |
| 60 | PAR16 | Med. | S2202 | 60PAR16/HAL/NSP | NSP 10° | 120V | 2500 | 4700 | 550 | CC-8 | 3 3/16" | Box | 15 |
| 60 | PAR16 | Med. | S2302 | 60PAR16/HAL/NSP | NSP 10° | 130V | 2500 | 4700 | 550 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S2203 | 75PAR16/HAL/NFL | NFL 30° | 120V | 2500 | 1800 | 850 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S2303 | 75PAR16/HAL/NFL | NFL 30° | 130V | 2500 | 1800 | 850 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S2204 | 75PAR16/HAL/NSP | NSP 10° | 120V | 2500 | 7000 | 850 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S2304 | 75PAR16/HAL/NSP | NSP 10° | 130V | 2500 | 7000 | 850 | CC-8 | 3 3/16" | Box | 15 |
| 50 | PAR20 | Med. | S2205 | 50PAR20/HAL/NFL | NFL 34° | 120V | 2500 | 1300 | 495 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S2305 | 50PAR20/HAL/NFL | NFL 34° | 130V | 2500 | 1300 | 495 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S2206 | 50PAR20/HAL/NSP | NSP 10° | 120V | 2500 | 4700 | 495 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S2306 | 50PAR20/HAL/NSP | NSP 10° | 130V | 2500 | 4700 | 495 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR30 | Med. | S2207 | 50PAR30/HAL/NFL | NFL 34° | 120V | 2500 | 1750 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2307 | 50PAR30/HAL/NFL | NFL 34° | 130V | 2500 | 1750 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2208 | 50PAR30/HAL/WFL | WFL 50° | 120V | 2500 | 460 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2308 | 50PAR30/HAL/WFL | WFL 50° | 130V | 2500 | 460 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2209 | 50PAR30/HAL/NSP | NSP 9° | 120V | 2500 | 7600 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2309 | 50PAR30/HAL/NSP | NSP 9° | 130V | 2500 | 7600 | 56+0 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2210 | 75PAR30/HAL/NFL | NFL 34° | 120V | 2500 | 3100 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2310 | 75PAR30/HAL/NFL | NFL 34° | 130V | 2500 | 3100 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2211 | 75PAR30/HAL/WFL | WFL 50° | 120V | 2500 | 770 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2311 | 75PAR30/HAL/WFL | WFL 50° | 130V | 2500 | 770 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2212 | 75PAR30/HAL/NSP | NSP 9° | 120V | 2500 | 13000 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2312 | 75PAR30/HAL/NSP | NSP 9° | 130V | 2500 | 13000 | 945 | CC-8 | 3 5/8" | Box | 15 |

Not Shown Actual Size



PAR38

PAR30LN

SATCO PAR HALOGEN LAMPS

QUALITY • VALUE • PERFORMANCE

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Avg. Rated | | | | Filament | M.O.L. | Pack Type | Mst. Ctn. |
|-------|-----------|------|-----------------|------------------|---------|------------|-------|-------|--------|----------|---------|-----------|-----------|
| | | | | | | Volts | Hours | CBCP* | Lumens | | | | |
| 50 | PAR30/LN | Med. | S2213 | 50PAR30/HAL/NFL | NFL 34° | 120V | 2500 | 1750 | 560 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2313 | 50PAR30/HAL/NFL | NFL 34° | 130V | 2500 | 1750 | 560 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2214 | 50PAR30/HAL/WFL | WFL 50° | 120V | 2500 | 460 | 560 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2314 | 50PAR30/HAL/WFL | WFL 50° | 130V | 2500 | 460 | 560 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2215 | 50PAR30/HAL/NSP | NSP 9° | 120V | 2500 | 7600 | 550 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2315 | 50PAR30/HAL/NSP | NSP 9° | 130V | 2500 | 7600 | 550 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2216 | 75PAR30/HAL/NFL | NFL 34° | 120V | 2500 | 3100 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2316 | 75PAR30/HAL/NFL | NFL 34° | 130V | 2500 | 3100 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2217 | 75PAR30/HAL/WFL | WFL 50° | 120V | 2500 | 770 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2317 | 75PAR30/HAL/WFL | WFL 50° | 130V | 2500 | 770 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2218 | 75PAR30/HAL/NSP | NSP 9° | 120V | 2500 | 13000 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2318 | 75PAR30/HAL/NSP | NSP 9° | 130V | 2500 | 13000 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 45 | PAR38 | Med. | S2219 | 45PAR38/HAL/FL | FL 30° | 120V | 2500 | 1380 | 465 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. | S2319 | 45PAR38/HAL/FL | FL 30° | 130V | 2500 | 1380 | 465 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. | S2220 | 45PAR38/HAL/NSP | NSP 9° | 120V | 2500 | 5000 | 465 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. | S2320 | 45PAR38/HAL/NSP | NSP 9° | 130V | 2500 | 5000 | 465 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. | S2221 | 75PAR38/HAL/FL | FL 30° | 120V | 2500 | 3200 | 960 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. | S2321 | 75PAR38/HAL/FL | FL 30° | 130V | 2500 | 3200 | 960 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. | S2222 | 75PAR38/HAL/NSP | NSP 9° | 120V | 2500 | 16000 | 960 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. | S2322 | 75PAR38/HAL/NSP | NSP 9° | 130V | 2500 | 16000 | 960 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. | S2223 | 90PAR38/HAL/FL | FL 30° | 120V | 2500 | 3800 | 1260 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. | S2323 | 90PAR38/HAL/FL | FL 30° | 130V | 2500 | 3800 | 1260 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. | S2224 | 90PAR38/HAL/NSP | NSP 9° | 120V | 2500 | 14000 | 1260 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. | S2324 | 90PAR38/HAL/NSP | NSP 9° | 130V | 2500 | 14000 | 1260 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. | S2225 | 120PAR38/HAL/FL | FL 30° | 120V | 2500 | 4700 | 1600 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. | S2325 | 120PAR38/HAL/FL | FL 30° | 130V | 2500 | 4700 | 1600 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. | S2226 | 120PAR38/HAL/NSP | NSP 9° | 120V | 2500 | 22000 | 1600 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. | S2326 | 120PAR38/HAL/NSP | NSP 9° | 130V | 2500 | 22000 | 1600 | CC-8 | 5 5/16" | Box | 15 |

Halogen

PAR14/PAR16/PAR20

Whiter light, brighter colors, precise beam control.



PAR14

PAR16

PAR20

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Avg. Rated | | CBCP | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------------|---------|------------|-------|------|--------|----------|---------|------------|-----------|
| | | | | | | Volts | Hours | | | | | | |
| 35 | PAR14 | Med. | S4658 | 35PAR14/CAP/WFL | WFL 50° | 120V | 2000 | 85 | 300 | CC-8 | 2 7/16" | Box | 6 |
| 60 | PAR16 | Med. | S4900 | 60PAR16/CAP/NFL | NFL 30° | 120V | 2000 | 1300 | 650 | CC-8 | 2 7/8" | Box | 15 |
| 60 | PAR16 | Med. | S4901 | 60PAR16/CAP/NFL | NFL 30° | 130V | 2000 | 1300 | 650 | CC-8 | 2 7/8" | Box | 15 |
| 60 | PAR16 | Med. | S4902 | 60PAR16/CAP/NSP | NSP 10° | 120V | 2000 | 5000 | 650 | CC-8 | 2 7/8" | Box | 15 |
| 60 | PAR16 | Med. | S4903 | 60PAR16/CAP/NSP | NSP 10° | 130V | 2000 | 5000 | 650 | CC-8 | 2 7/8" | Box | 15 |
| 75 | PAR16 | Med. | S4904 | 75PAR16/CAP/NFL | NFL 30° | 120V | 2000 | 1900 | 900 | CC-8 | 2 7/8" | Box | 15 |
| 75 | PAR16 | Med. | S4905 | 75PAR16/CAP/NFL | NFL 30° | 130V | 2000 | 1900 | 900 | CC-8 | 2 7/8" | Box | 15 |
| 75 | PAR16 | Med. | S4906 | 75PAR16/CAP/NSP | NSP 10° | 120V | 2000 | 7500 | 900 | CC-8 | 2 7/8" | Box | 15 |
| 75 | PAR16 | Med. | S4907 | 75PAR16/CAP/NSP | NSP 10° | 130V | 2000 | 7500 | 900 | CC-8 | 2 7/8" | Box | 15 |
| 35 | PAR20 | Med. | S4908 | 35PAR20/CAP/NFL | NFL 30° | 120V | 2500 | 800 | 360 | CC-8 | 3 1/4" | Box | 15 |
| 35 | PAR20 | Med. | S4663 | 35PAR20/CAP/NFL | NFL 30° | 130V | 2500 | 800 | 360 | CC-8 | 3 1/4" | Box | 15 |
| 35 | PAR20 | Med. | S4909 | 35PAR20/CAP/NSP | NSP 10° | 120V | 2500 | 3000 | 360 | CC-8 | 3 1/4" | Box | 15 |
| 35 | PAR20 | Med. | S4661 | 35PAR20/CAP/NSP | NSP 10° | 130V | 2500 | 3000 | 360 | CC-8 | 3 1/4" | Box | 15 |
| 35 | PAR20 | Med. | S4910 | 35PAR20/CAP/WFL | WFL 40° | 120V | 2500 | 500 | 360 | CC-8 | 3 1/8" | Box | 15 |
| 35 | PAR20 | Med. | S4665 | 35PAR20/CAP/WFL | WFL 40° | 120V | 2500 | 500 | 360 | CC-8 | 3 1/8" | Box | 15 |
| 50 | PAR20 | Med. | S4911 | 50PAR20/CAP/NFL | NFL 30° | 120V | 2500 | 1400 | 550 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S4912 | 50PAR20/CAP/NFL | NFL 30° | 130V | 2500 | 1400 | 550 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S4913 | 50PAR20/CAP/NSP | NSP 10° | 120V | 2500 | 6200 | 550 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S4914 | 50PAR20/CAP/NSP | NSP 10° | 130V | 2500 | 6200 | 550 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S4666 | 50PAR20/CAP/WFL | WFL 40° | 120V | 2500 | 900 | 550 | CC-8 | 3 1/8" | Box | 15 |

Halogen **PAR30** Short & Long Neck

Whiter light, brighter colors, precise beam control.

Not Shown Actual Size



PAR30 Short Neck



PAR30 Long Neck

reflector

SHORT NECK

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP* | Lumens | Filament | M.O.L. | Pack Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------------|---------|-------|------------------|-------|--------|----------|--------|-----------|-----------|
| 50 | PAR30 | Med. | S4915 | 50PAR30/CAP/FL | FL 40° | 120V | 2500 | 1300 | 600 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4916 | 50PAR30/CAP/FL | FL 40° | 130V | 2500 | 1300 | 600 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4917 | 50PAR30/CAP/NFL | NFL 25° | 120V | 2500 | 2300 | 660 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4918 | 50PAR30/CAP/NFL | NFL 25° | 130V | 2500 | 2300 | 660 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4919 | 50PAR30/CAP/NSP | NSP 9° | 120V | 2500 | 8800 | 660 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4920 | 50PAR30/CAP/NSP | NSP 9° | 130V | 2500 | 8800 | 660 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4921 | 75PAR30/CAP/FL | FL 40° | 120V | 2500 | 2000 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4922 | 75PAR30/CAP/FL | FL 40° | 130V | 2500 | 2000 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4923 | 75PAR30/CAP/NFL | NFL 25° | 120V | 2500 | 4000 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4924 | 75PAR30/CAP/NFL | NFL 25° | 130V | 2500 | 4000 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4925 | 75PAR30/CAP/NSP | NSP 9° | 120V | 2500 | 15400 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4926 | 75PAR30/CAP/NSP | NSP 9° | 130V | 2500 | 15400 | 1130 | CC-8 | 3 5/8" | Box | 15 |

LONG NECK

| | | | | | | | | | | | | | |
|----|----------|------|--------------|-------------------|---------|------|------|-------|------|------|--------|-----|----|
| 35 | PAR30/LN | Med. | S2654 | 35PAR30LN/CAP/WFL | WFL 50° | 120V | 2500 | 450 | 450 | CC-8 | 4 5/8" | Box | 15 |
| 35 | PAR30/LN | Med. | S2655 | 35PAR30LN/CAP/NSP | NSP 9° | 120V | 2500 | 5700 | 450 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4927 | 50PAR30LN/CAP/WFL | WFL 50° | 120V | 2500 | 660 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4928 | 50PAR30LN/CAP/WFL | WFL 50° | 130V | 2500 | 660 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4929 | 50PAR30LN/CAP/NFL | NFL 25° | 120V | 2500 | 2300 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4930 | 50PAR30LN/CAP/NFL | NFL 25° | 130V | 2500 | 2300 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4931 | 50PAR30LN/CAP/NSP | NSP 9° | 120V | 2500 | 8800 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4932 | 50PAR30LN/CAP/NSP | NSP 9° | 130V | 2500 | 8800 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4933 | 75PAR30LN/CAP/WFL | WFL 50° | 120V | 2500 | 1100 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4934 | 75PAR30LN/CAP/WFL | WFL 50° | 130V | 2500 | 1100 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4935 | 75PAR30LN/CAP/NFL | NFL 25° | 120V | 2500 | 4000 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4936 | 75PAR30LN/CAP/NFL | NFL 25° | 130V | 2500 | 4000 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4937 | 75PAR30LN/CAP/NSP | NSP 9° | 120V | 2500 | 15400 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4938 | 75PAR30LN/CAP/NSP | NSP 9° | 130V | 2500 | 15400 | 1130 | CC-8 | 4 5/8" | Box | 15 |

Reflectors **PAR38**

Not Shown Actual Size

Whiter light,
brighter colors,
precise beam
control.



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated | | CBCP* | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|-----------|--------------------|----------------|---------|-------|------------|-------|-------|--------|----------|--------|---------------|--------------|
| | | | | | | | Hours | | | | | | | |
| 45 | PAR38 | Med. Skt. | S4939 | 45PAR/CAP/FL | FL 30° | 120V | 2500 | 1500 | 560 | CC-8 | 5 5/16" | Box | 15 | |
| 45 | PAR38 | Med. Skt. | S4940 | 45PAR/CAP/FL | FL 30° | 130V | 2500 | 1500 | 560 | CC-8 | 5 5/16" | Box | 15 | |
| 45 | PAR38 | Med. Skt. | S4941 | 45PAR/CAP/NSP | NSP 9° | 120V | 2500 | 10000 | 560 | CC-8 | 5 5/16" | Box | 15 | |
| 45 | PAR38 | Med. Skt. | S4942 | 45PAR/CAP/NSP | NSP 9° | 130V | 2500 | 10000 | 560 | CC-8 | 5 5/16" | Box | 15 | |
| 45 | PAR38 | Med. Skt. | S4630 | 45PAR/CAP/WFL | WFL 50° | 130V | 2500 | 700 | 560 | CC-8 | 5 5/16" | Box | 15 | |
| 60 | PAR38 | Med. Skt. | S4943 | 60PAR/CAP/FL | FL 30° | 120V | 3000 | 2500 | 850 | CC-8 | 5 5/16" | Box | 15 | |
| 60 | PAR38 | Med. Skt. | S4944 | 60PAR/CAP/FL | FL 30° | 130V | 3000 | 2500 | 850 | CC-8 | 5 5/16" | Box | 15 | |
| 60 | PAR38 | Med. Skt. | S4945 | 60PAR/CAP/NSP | NSP 9° | 120V | 3000 | 16000 | 850 | CC-8 | 5 5/16" | Box | 15 | |
| 60 | PAR38 | Med. Skt. | S4946 | 60PAR/CAP/NSP | NSP 9° | 130V | 3000 | 16000 | 850 | CC-8 | 5 5/16" | Box | 15 | |
| 75 | PAR38 | Med. Skt. | S4964 | 75PAR/CAP/FL | FL 30° | 120V | 2500 | 3150 | 1060 | CC-8 | 5 5/16" | Box | 15 | |
| 75 | PAR38 | Med. Skt. | S4965 | 75PAR/CAP/FL | FL 30° | 130V | 2500 | 3150 | 1060 | CC-8 | 5 5/16" | Box | 15 | |
| 75 | PAR38 | Med. Skt. | S4966 | 75PAR/CAP/NSP | NSP 9° | 120V | 2500 | 19200 | 1060 | CC-8 | 5 5/16" | Box | 15 | |
| 75 | PAR38 | Med. Skt. | S4967 | 75PAR/CAP/NSP | NSP 9° | 130V | 2500 | 19200 | 1060 | CC-8 | 5 5/16" | Box | 15 | |
| 75 | PAR38 | Med. Skt. | S4631 | 75PAR/CAP/WFL | WFL 50° | 130V | 2500 | 1300 | 1060 | CC-8 | 5 5/16" | Box | 15 | |
| 90 | PAR38 | Med. Skt. | S4968 | 90PAR/CAP/FL | FL 30° | 120V | 2500 | 3500 | 1310 | CC-8 | 5 5/16" | Box | 15 | |
| 90 | PAR38 | Med. Skt. | S4969 | 90PAR/CAP/FL | FL 30° | 130V | 2500 | 3500 | 1310 | CC-8 | 5 5/16" | Box | 15 | |
| 90 | PAR38 | Med. Skt. | S4970 | 90PAR/CAP/NSP | NSP 9° | 120V | 2500 | 19000 | 1310 | CC-8 | 5 5/16" | Box | 15 | |
| 90 | PAR38 | Med. Skt. | S4971 | 90PAR/CAP/NSP | NSP 9° | 130V | 2500 | 19000 | 1310 | CC-8 | 5 5/16" | Box | 15 | |
| 90 | PAR38 | Med. Skt. | S4950 | 90PAR/CAP/WSP | WSP 12° | 120V | 2500 | 14300 | 1310 | CC-8 | 5 5/16" | Box | 15 | |
| 90 | PAR38 | Med. Skt. | S4951 | 90PAR/CAP/WSP | WSP 12° | 130V | 2500 | 14300 | 1310 | CC-8 | 5 5/16" | Box | 15 | |
| 90 | PAR38 | Med. Skt. | S4632 | 90PAR/CAP/NFL | NFL 25° | 130V | 2500 | 4700 | 1310 | CC-8 | 5 5/16" | Box | 15 | |
| 90 | PAR38 | Med. Skt. | S4633 | 90PAR/CAP/WFL | WFL 50° | 130V | 2500 | 1600 | 1310 | CC-8 | 5 5/16" | Box | 15 | |
| 120 | PAR38 | Med. Skt. | S4972 | 120PAR/CAP/FL | FL 30° | 120V | 3000 | 4600 | 1800 | CC-8 | 5 5/16" | Box | 15 | |
| 120 | PAR38 | Med. Skt. | S4973 | 120PAR/CAP/FL | FL 30° | 130V | 3000 | 4600 | 1800 | CC-8 | 5 5/16" | Box | 15 | |
| 120 | PAR38 | Med. Skt. | S4974 | 120PAR/CAP/SP | SP 10° | 120V | 3000 | 22500 | 1800 | CC-8 | 5 5/16" | Box | 15 | |
| 120 | PAR38 | Med. Skt. | S4975 | 120PAR/CAP/SP | SP 10° | 130V | 3000 | 22500 | 1800 | CC-8 | 5 5/16" | Box | 15 | |
| 120 | PAR38 | Med. Skt. | S4634 | 120PAR/CAP/WFL | WFL 50° | 130V | 3000 | 2000 | 1800 | CC-8 | 5 5/16" | Box | 15 | |
| 250 | PAR38 | Med. Skt. | S4947 | 250PAR/CAP/FL | FL 30° | 120V | 4500 | 4500 | 3600 | CC-8 | 5 5/16" | Box | 6 | |
| 250 | PAR38 | Med. Skt. | S4948 | 250PAR/CAP/SP | SP 10° | 120V | 4500 | 46500 | 3600 | CC-8 | 5 5/16" | Box | 6 | |

reflectors

Lights

1500 Hours/120V

G8 1" Round
Glossy White
 Candelabra Base
 (120 Volt)
S3864 10 Watt
 Packing:
 Individually Boxed
 1000/Master, 25/Inner



G12 1 1/2" Round
Clear
 Candelabra Base
 (120 Volt)
S3844 10 Watt
S3845 15 Watt
S3846 25 Watt
S3847 40 Watt
 Packing:
 Individually Boxed
 500/Master, 25/Inner



G12 1 1/2" Pear
Satin White
 Candelabra Base
 (120 Volt)
S3879 15 Watt
S3863 25 Watt
 Packing:
 Individually Boxed
 500/Master, 25/Inner



G12 1 1/2" Round
Satin White
 Candelabra Base
S3830 10 Watt
 (120 Volt)
 Packing:
 Individually Boxed
 500/Master, 25/Inner



Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-------------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 10 | G8 | Cand. | S3864 | 10G8/W | White | 120V | 1500 | 50 | C7A | 1 7/8" | Box | 1000/25 |
| 10 | G12 1/2 | Cand. | S3844 | 10G12 1/2 | Clear | 120V | 1500 | 60 | C7A | 2 3/8" | Box | 500/25 |
| 10 | G12 1/2 | Cand. | S3830 | 10G12 1/2/W | White | 120V | 1500 | 50 | C7A | 2 3/8" | Box | 500/25 |
| 15 | G12 1/2 | Cand. | S3845 | 15G12 1/2 | Clear | 120V | 1500 | 100 | C7A | 2 3/8" | Box | 500/25 |
| 25 | G12 1/2 | Cand. | S3846 | 25G12 1/2 | Clear | 120V | 1500 | 180 | C7A | 2 3/8" | Box | 500/25 |
| 40 | G12 1/2 | Cand. | S3847 | 40G12 1/2 | Clear | 120V | 1500 | 370 | C7A | 2 3/8" | Box | 500/25 |
| 15 | G12 1/2 | Cand. | S3879 | 15G12 1/2/W | White | 120V | 1500 | 100 | C7A | 2 3/8" | Box | 500/25 |
| 25 | G12 1/2 | Cand. | S3863 | 25G12 1/2/W | White | 120V | 1500 | 180 | C7A | 2 3/8" | Box | 500/25 |

decorative incandescent lamps

Globe Lights

1500 Hours



S3834 10 Watt Blue



S3835 10 Watt Green



S3836 10 Watt Amber



S3837 10 Watt Pink



S3833 10 Watt Red

**G12 1 1/2" Round
Transparent Colors**

Candelabra Base (120 Volt)

Packing: Individually Boxed
500/Master, 25/Inner

Shown Actual Size



G16 1/2 2 1/8"

Silver Crown

Candelabra Base
(120 Volt)

S3244 25 Watt

S3245 40 Watt

S3246 60 Watt

Packing: Individually Boxed
500/Master, 25/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|--------------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 10 | G12 1/2 | Cand. | S3833 | 10G12 1/2/R | Red | 120V | 1500 | n/a | C7A | 2 3/8" | Box | 500/25 |
| 10 | G12 1/2 | Cand. | S3834 | 10G12 1/2/B | Blue | 120V | 1500 | n/a | C7A | 2 3/8" | Box | 500/25 |
| 10 | G12 1/2 | Cand. | S3835 | 10G12 1/2/G | Green | 120V | 1500 | n/a | C7A | 2 3/8" | Box | 500/25 |
| 10 | G12 1/2 | Cand. | S3836 | 10G12 1/2/A | Amber | 120V | 1500 | n/a | C7A | 2 3/8" | Box | 500/25 |
| 10 | G12 1/2 | Cand. | S3837 | 10G12 1/2/PK | Pink | 120V | 1500 | n/a | C7A | 2 3/8" | Box | 500/25 |
| 25 | G16 1/2 | Cand. | S3244 | 25G16 1/2/SL | Silver | 120V | 1500 | 232 | CC-2V | 3" | Box | 500/25 |
| 40 | G16 1/2 | Cand. | S3245 | 40G16 1/2/SL | Silver | 120V | 1500 | 384 | CC-2V | 3" | Box | 500/25 |
| 60 | G16 1/2 | Cand. | S3246 | 60G16 1/2/SL | Silver | 120V | 1500 | 672 | CC-2V | 3" | Box | 500/25 |

decorative incandescent lamps

G16 1/2 Brass Base



Globe Lights 2 1/8"

1500 Hours



Satin White



Clear



Glossy White

Candelabra Base
(120 Volt)

- S3824** 15 Watt
- S3825** 25 Watt
- S3826** 40 Watt
- S3832** 60 Watt

Packing: Individually Boxed
500/Master, 25/Inner

Candelabra Base
(120 Volt)

- S3821** 15 Watt
- S3822** 25 Watt
- S3823** 40 Watt
- S3831** 60 Watt

Packing: Individually Boxed
500/Master, 25/Inner

Candelabra Base
(120 Volt)

- S3236** 15 Watt
- S3260** 25 Watt
- S3261** 40 Watt
- S3271** 60 Watt

Packing: Individually Boxed
500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|--------------|-------|------------------|--------|----------|--------|------------|----------------------|
| 15 | G16 1/2 | Cand. | S3821 | 15G16 1/2 | Clear | 120V | 1500 | 114 | C7A | 3" | Box | 500/25 |
| 15 | G16 1/2 | Cand. | S3824 | 15G16 1/2W | Sat. White | 120V | 1500 | 94 | C7A | 3" | Box | 500/25 |
| 15 | G16 1/2 | Cand. | S3236 | 15G16 1/2W | Gloss. White | 120V | 1500 | 94 | C7A | 3" | Box | 500/25 |
| 25 | G16 1/2 | Cand. | S3822 | 25G16 1/2 | Clear | 120V | 1500 | 232 | C7A | 3" | Box | 500/25 |
| 25 | G16 1/2 | Cand. | S3825 | 25G16 1/2W | Sat. White | 120V | 1500 | 202 | C7A | 3" | Box | 500/25 |
| 25 | G16 1/2 | Cand. | S3260 | 25G16 1/2W | Gloss White | 120V | 1500 | 202 | C7A | 3" | Box | 500/25 |
| 40 | G16 1/2 | Cand. | S3823 | 40G16 1/2 | Clear | 120V | 1500 | 384 | CC-2V | 3" | Box | 500/25 |
| 40 | G16 1/2 | Cand. | S3826 | 40G16 1/2W | Sat. White | 120V | 1500 | 348 | CC-2V | 3" | Box | 500/25 |
| 40 | G16 1/2 | Cand. | S3261 | 40G16 1/2W | Gloss White | 120V | 1500 | 348 | CC-2V | 3" | Box | 500/25 |
| 60 | G16 1/2 | Cand. | S3831 | 60G16 1/2 | Clear | 120V | 1500 | 672 | CC-2V | 3" | Box | 500/25 |
| 60 | G16 1/2 | Cand. | S3832 | 60G16 1/2W | Sat. White | 120V | 1500 | 630 | CC-2V | 3" | Box | 500/25 |
| 60 | G16 1/2 | Cand. | S3271 | 60G16 1/2W | Gloss. White | 120V | 1500 | 630 | CC-2V | 3" | Box | 500/25 |

decorative incandescent lamps

2500 Hours / 130 Volt

Globe Lights 2 1/8"



Clear



Satin White

*Candelabra Base
(130 Volt)*

- A3921** 15 Watt
- A3922** 25 Watt
- A3923** 40 Watt
- A3931** 60 Watt

*Packing: Individually Boxed
500/Master, 25/Inner*

*Candelabra Base
(130 Volt)*

- A3924** 15 Watt
- A3925** 25 Watt
- A3926** 40 Watt
- A3932** 60 Watt

*Packing: Individually Boxed
500/Master, 25/Inner*

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 15 | G16 1/2 | Cand. | A3921 | 15G16 1/2 | Clear | 130V | 2500 | 98 | C7A | 3" | Box | 500/25 |
| 15 | G16 1/2 | Cand. | A3924 | 15G16 1/2W | White | 130V | 2500 | 83 | C7A | 3" | Box | 500/25 |
| 25 | G16 1/2 | Cand. | A3922 | 25G16 1/2 | Clear | 130V | 2500 | 186 | C7A | 3" | Box | 500/25 |
| 25 | G16 1/2 | Cand. | A3925 | 25G16 1/2W | White | 130V | 2500 | 162 | C7A | 3" | Box | 500/25 |
| 40 | G16 1/2 | Cand. | A3923 | 40G16 1/2 | Clear | 130V | 2500 | 360 | CC-2V | 3" | Box | 500/25 |
| 40 | G16 1/2 | Cand. | A3926 | 40G16 1/2W | White | 130V | 2500 | 325 | CC-2V | 3" | Box | 500/25 |
| 60 | G16 1/2 | Cand. | A3931 | 60G16 1/2 | Clear | 130V | 2500 | 642 | CC-2V | 3" | Box | 500/25 |
| 60 | G16 1/2 | Cand. | A3932 | 60G16 1/2W | White | 130V | 2500 | 564 | CC-2V | 3" | Box | 500/25 |

decorative incandescent lamps

Globe Lights

1000 Hours/130 Volts



G14

White
Euro Base
(130 Volt)
S3398 40 Watt
Packing:
Individually Boxed
500/Master, 25/Inner



G14

Clear
Euro Base
(130 Volt)
S3397 40 Watt
Packing:
Individually Boxed
500/Master, 25/Inner



G17

**Medicine
Cabinet
Bulb
Frosted**
E27 Base
(130 Volt)
S3967 40 Watt
Packing:
Individually Boxed
500/Master, 25/Inner



G17

**Medicine
Cabinet
Bulb
White**
E27 Base
(130 Volt)
S3968 40 Watt
Packing:
Individually Boxed
500/Master, 25/Inner

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-----------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 40 | G14 | E14/Euro. | S3397 | 40G14 | Clear | 130V | 1000 | 368 | CC9 | 31/8 | Box | 500/25 |
| 40 | G14 | E14/Euro | S3398 | 40G14/W | White | 130V | 1000 | 320 | CC9 | 31/8 | Box | 500/25 |
| 40 | G17 | E27/Med. | S3967 | 40G17/IF | Frost | 130V | 1000 | 348 | CC9 | 31/8 | Box | 500/25 |
| 40 | G17 | E27/Med. | S3968 | 40G17/W | White | 130V | 1000 | 320 | CC9 | 31/8 | Box | 500/25 |

decorative incandescent lamps

1500 Hours / 120 Volt

Globe Lights

Not Shown Actual Size

G16 1/2 2 1/8"

Glossy White
Medium Base
(120 Volt)

- S3841** 25 Watt
- S3842** 40 Watt
- S3843** 60 Watt

Packing:
Individually Boxed
500/Master, 25/Inner



G16 1/2 2 1/8"
Clear

Medium Base
(120 Volt)

- S3838** 25 Watt
- S3839** 40 Watt
- S3840** 60 Watt

Packing:
Individually Boxed
500/Master, 25/Inner



G18 1/2 2 3/8"

Glossy White
Medium Base
(120 Volt)

- S3827** 25 Watt
- S3828** 40 Watt
- S3829** 60 Watt

Packing:
Individually Boxed
250/Master, 25/Inner



G18 1/2 2 3/8"
Clear

Medium Base
(120 Volt)

- S3887** 25 Watt
- S3888** 40 Watt
- S3889** 60 Watt

Packing:
Individually Boxed
250/Master, 25/Inner



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|------------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | G16 1/2 | Med. | S3838 | 25G16 1/2 | Clear | 120V | 1500 | 210 | CC-2V | 3 1/4" | Box | 500/25 |
| 25 | G16 1/2 | Med. | S3841 | 25G16 1/2W | White | 120V | 1500 | 160 | CC-2V | 3 1/4" | Box | 500/25 |
| 40 | G16 1/2 | Med. | S3839 | 40G16 1/2 | Clear | 120V | 1500 | 370 | CC-2V | 3 1/4" | Box | 500/25 |
| 40 | G16 1/2 | Med. | S3842 | 40G16 1/2W | White | 120V | 1500 | 320 | CC-2V | 3 1/4" | Box | 500/25 |
| 60 | G16 1/2 | Med. | S3840 | 60G16 1/2 | Clear | 120V | 1500 | 650 | CC-2V | 3 1/4" | Box | 500/25 |
| 60 | G16 1/2 | Med. | S3843 | 60G16 1/2W | White | 120V | 1500 | 550 | CC-2V | 3 1/4" | Box | 500/25 |
| 25 | G18 1/2 | Med. | S3887 | 25G18 1/2 | Clear | 120V | 1500 | 158 | C-9 | 3 1/2" | Box | 250/25 |
| 25 | G18 1/2 | Med. | S3827 | 25G18 1/2W | White | 120V | 1500 | 120 | C-9 | 3 1/2" | Box | 250/25 |
| 40 | G18 1/2 | Med. | S3888 | 40G18 1/2 | Clear | 120V | 1500 | 368 | C-9 | 3 1/2" | Box | 250/25 |
| 40 | G18 1/2 | Med. | S3828 | 40G18 1/2W | White | 120V | 1500 | 280 | C-9 | 3 1/2" | Box | 250/25 |
| 60 | G18 1/2 | Med. | S3889 | 60G18 1/2 | Clear | 120V | 1500 | 610 | C-9 | 3 1/2" | Box | 250/25 |
| 60 | G18 1/2 | Med. | S3829 | 60G18 1/2W | White | 120V | 1500 | 530 | C-9 | 3 1/2" | Box | 250/25 |

decorative incandescent lamps

G25 Brass Base

SATCO®

Globe Lights 3 1/8" 120V

2500 Hours

Clear

Medium Base
(120 Volt)

- S3447** 25 Watt
- S3448** 40 Watt
- S3449** 60 Watt
- S3450** 100 Watt

Packing:
Individually Boxed
72/Master, 6/Inner



Shown Actual Size



White

Medium Base
(120 Volt)

- S3440** 25 Watt
- S3441** 40 Watt
- S3442** 60 Watt
- S3443** 100 Watt

Packing:
Individually Boxed
72/Master, 6/Inner



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | G25 | Med. | S3447 | 25G25 | Clear | 120V | 2500 | 212 | CC-9 | 4 3/8" | Box | 72/6 |
| 25 | G25 | Med. | S3440 | 25G25/W | White | 120V | 2500 | 187 | CC-9 | 4 3/8" | Box | 72/6 |
| 40 | G25 | Med. | S3448 | 40G25 | Clear | 120V | 2500 | 384 | CC-9 | 4 3/8" | Box | 72/6 |
| 40 | G25 | Med. | S3441 | 40G25/W | White | 120V | 2500 | 340 | CC-9 | 4 3/8" | Box | 72/6 |
| 60 | G25 | Med. | S3449 | 60G25 | Clear | 120V | 2500 | 650 | CC-9 | 4 3/8" | Box | 72/6 |
| 60 | G25 | Med. | S3442 | 60G25/W | White | 120V | 2500 | 575 | CC-9 | 4 3/8" | Box | 72/6 |
| 100 | G25 | Med. | S3450 | 100G25 | Clear | 120V | 2500 | 1000 | CC-9 | 4 3/8" | Box | 72/6 |
| 100 | G25 | Med. | S3443 | 100G25/W | White | 120V | 2500 | 920 | CC-9 | 4 3/8" | Box | 72/6 |

decorative incandescent lamps

3000 Hours

Globe Lights 3 1/8" 130V




Shown Actual Size



Clear
 Medium Base
 (130 Volt)
A3647 25 Watt
A3648 40 Watt
A3649 60 Watt
A3650 100 Watt
 Packing:
 Individually Boxed
 72/Master, 6/Inner



White
 Medium Base
 (130 Volt)
A3640 25 Watt
A3641 40 Watt
A3642 60 Watt
A3643 100 Watt
 Packing:
 Individually Boxed
 72/Master, 6/Inner



decorative incandescent lamps

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|---------------------|
| 25 | G25 | Med. | A3647 | 25G25 | Clear | 130V | 3000 | 193 | CC-9 | 4 3/8" | Box | 72/6 |
| 25 | G25 | Med. | A3640 | 25G25/W | White | 130V | 3000 | 167 | CC-9 | 4 3/8" | Box | 72/6 |
| 40 | G25 | Med. | A3648 | 40G25 | Clear | 130V | 3000 | 360 | CC-9 | 4 3/8" | Box | 72/6 |
| 40 | G25 | Med. | A3641 | 40G25/W | White | 130V | 3000 | 320 | CC-9 | 4 3/8" | Box | 72/6 |
| 60 | G25 | Med. | A3649 | 60G25 | Clear | 130V | 3000 | 642 | CC-9 | 4 3/8" | Box | 72/6 |
| 60 | G25 | Med. | A3642 | 60G25/W | White | 130V | 3000 | 564 | CC-9 | 4 3/8" | Box | 72/6 |
| 100 | G25 | Med. | A3650 | 100G25 | Clear | 130V | 3000 | 1000 | CC-9 | 4 3/8" | Box | 72/6 |
| 100 | G25 | Med. | A3643 | 100G25/W | White | 130V | 3000 | 920 | CC-9 | 4 3/8" | Box | 72/6 |

G25 Brass Base



Globe Lights 3 1/8" 120V

2500 Hours

3 Pack

Clear

Medium Base
(120 Volt)

S4048 40 Watt

S4049 60 Watt

Packing: 3/Box
40 3-Packs /Master
Sold Per Pack



White

Medium Base
(120 Volt)

S4041 40 Watt

S4042 60 Watt

Packing: 3/Box
40 3-Packs /Master
Sold Per Pack



Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-------------|--------|-------|------------------|--------|----------|--------|------------|-----------|
| 40 | G25 | Med. | S4048 | 40G25/3PK | Clear | 120V | 2500 | 384 | CC-9 | 4 3/8" | Box/3 | 40 |
| 40 | G25 | Med. | S4041 | 40G25/W/3PK | White | 120V | 2500 | 340 | CC-9 | 4 3/8" | Box/3 | 40 |
| 60 | G25 | Med. | S4049 | 60G25/3PK | Clear | 120V | 2500 | 650 | CC-9 | 4 3/8" | Box/3 | 40 |
| 60 | G25 | Med. | S4042 | 60G25/W/3PK | White | 120V | 2500 | 575 | CC-9 | 4 3/8" | Box/3 | 40 |

decorative incandescent lamps

ALLURA®

Brass Base **G25**

3000 Hours

Globe Lights 3 1/8" 130V



Clear
Medium Base
(130 Volt)
A4148 40 Watt
A4149 60 Watt
Packing: 3/Box
40 3-Packs /Master
Sold Per Pack



Shown Actual Size



3 Pack



White
Medium Base
(130 Volt)
A4141 40 Watt
A4142 60 Watt
Packing: 3/Box
40 3-Packs /Master
Sold Per Pack

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-------------|--------|-------|------------------|--------|----------|--------|------------|-----------|
| 40 | G25 | Med. | A4148 | 40G25/3PK | Clear | 130V | 3000 | 360 | CC-9 | 4 3/8" | Box/3 | 40 |
| 40 | G25 | Med. | A4141 | 40G25/W/3PK | White | 130V | 3000 | 320 | CC-9 | 4 3/8" | Box/3 | 40 |
| 60 | G25 | Med. | A4149 | 60G25/3PK | Clear | 130V | 3000 | 642 | CC-9 | 4 3/8" | Box/3 | 40 |
| 60 | G25 | Med. | A4142 | 60G25/W/3PK | White | 130V | 3000 | 564 | CC-9 | 4 3/8" | Box/3 | 40 |

decorative incandescent lamps

G25 & G30 Brass Base



Globe Lights

120V

Not Shown Actual Size

G25 3 1/8"

Silver Crown

Medium Base

1500 Hrs. Average Life
(120 Volt)

S3860 25 Watt

S3861 40 Watt

S3862 60 Watt

Packing: Individually Boxed
72/Master, 6/Inner



G30 3 3/4"

Medium Base

2500 Hrs. Average Life
(120 Volt)

Clear

S3651 25 Watt

S3652 40 Watt

S3670 60 Watt

White

S3653 25 Watt

S3671 40 Watt

S3672 60 Watt

Packing:
Individually Boxed
72/Master, 6/Inner



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|---------------------|
| 25 | G25 | Med. | S3860 | 25G25/SL | Silver | 120V | 1500 | 170 | CC-9 | 4 3/8" | Box | 72/6 |
| 40 | G25 | Med. | S3861 | 40G25/SL | Silver | 120V | 1500 | 280 | CC-9 | 4 3/8" | Box | 72/6 |
| 60 | G25 | Med. | S3862 | 60G25/SL | Silver | 120V | 1500 | 512 | CC-9 | 4 3/8" | Box | 72/6 |
| 25 | G30 | Med. | S3651 | 25G30 | Clear | 120V | 2500 | 212 | CC-9 | 5 1/8" | Box | 72/6 |
| 25 | G30 | Med. | S3653 | 25G30W | White | 120V | 2500 | 187 | CC-9 | 5 1/8" | Box | 72/6 |
| 40 | G30 | Med. | S3652 | 40G30 | Clear | 120V | 2500 | 384 | CC-9 | 5 1/8" | Box | 72/6 |
| 40 | G30 | Med. | S3671 | 40G30/W | White | 120V | 2500 | 320 | CC-9 | 5 1/8" | Box | 72/6 |
| 60 | G30 | Med. | S3670 | 60G30 | Clear | 120V | 2500 | 650 | CC-9 | 5 1/8" | Box | 72/6 |
| 60 | G30 | Med. | S3672 | 60G30/W | White | 120V | 2500 | 575 | CC-9 | 5 1/8" | Box | 72/6 |

decorative incandescent lamps

4000 Hours / 120 Volt

Globe Lights 5"



White

- Medium Base
- S3000** 25 Watt
- S3001** 40 Watt
- S3002** 60 Watt
- S3003** 100 Watt
- S3004** 150 Watt

Packing: Individually Boxed
24/Master, 6/Inner



Clear

- Medium Base
- S3010** 25 Watt
- S3011** 40 Watt
- S3012** 60 Watt
- S3013** 100 Watt
- S3014** 150 Watt

Packing: Individually Boxed
24/Master, 6/Inner

Not Shown Actual Size


| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | G40 | Med. | S3010 | 25G40 | Clear | 120V | 4000 | 120 | C-9 | 6 3/4" | Box | 24/6 |
| 25 | G40 | Med. | S3000 | 25G40/W | White | 120V | 4000 | 110 | C-9 | 6 3/4" | Box | 24/6 |
| 40 | G40 | Med. | S3011 | 40G40 | Clear | 120V | 4000 | 300 | C-9 | 6 3/4" | Box | 24/6 |
| 40 | G40 | Med. | S3001 | 40G40/W | White | 120V | 4000 | 280 | C-9 | 6 3/4" | Box | 24/6 |
| 60 | G40 | Med. | S3012 | 60G40 | Clear | 120V | 4000 | 580 | C-9 | 6 3/4" | Box | 24/6 |
| 60 | G40 | Med. | S3002 | 60G40/W | White | 120V | 4000 | 550 | C-9 | 6 3/4" | Box | 24/6 |
| 100 | G40 | Med. | S3013 | 100G40 | Clear | 120V | 4000 | 1150 | C-9 | 6 3/4" | Box | 24/6 |
| 100 | G40 | Med. | S3003 | 100G40/W | White | 120V | 4000 | 1050 | C-9 | 6 3/4" | Box | 24/6 |
| 150 | G40 | Med. | S3014 | 150G40 | Clear | 120V | 4000 | 1700 | C-9 | 6 3/4" | Box | 24/6 |
| 150 | G40 | Med. | S3004 | 150G40/W | White | 120V | 4000 | 1550 | C-9 | 6 3/4" | Box | 24/6 |

decorative incandescent lamps

Bulbs

120 Volt / 1500 Hours

Candelabra Base



Clear

Clear

Clear

Clear

Clear

S3272 10 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

S3273 15 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

S3274 25 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

S3275 40 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

S3262 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|----------------------|
| 10 | CA-7 | Cand. | S3272 | 10CA7 | Clear | 120V | 1500 | 80 | C-7A | 3" | Box | 500/25 |
| 15 | CA-8 | Cand. | S3273 | 15CA8 | Clear | 120V | 1500 | 100 | C-7A | 3 5/8" | Box | 500/25 |
| 25 | CA-8 | Cand. | S3274 | 25CA8 | Clear | 120V | 1500 | 210 | CC-2V | 3 5/8" | Box | 500/25 |
| 40 | CA-9 1/2 | Cand. | S3275 | 40CA9 1/2 | Clear | 120V | 1500 | 370 | CC-2V | 3 15/16" | Box | 500/25 |
| 60 | CA-10 | Cand. | S3262 | 60CA10 | Clear | 120V | 1500 | 672 | CC-2V | 4 1/4" | Box | 500/25 |

decorative incandescent lamps

1500 Hours / 120 Volt

Candelabra Base



Frosted

Frosted

Frosted

Frosted

Frosted

S3263 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

S3279 40 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

S3278 25 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

S3277 15 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

S3276 10 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-------------|---------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 10 | CA-7 | Cand. | S3276 | 10CA7/F | Frosted | 120V | 1500 | 70 | C7A | 3" | Box | 500/25 |
| 15 | CA-8 | Cand. | S3277 | 15CA8/F | Frosted | 120V | 1500 | 95 | C7A | 3 5/8" | Box | 500/25 |
| 25 | CA-8 | Cand. | S3278 | 25CA8/F | Frosted | 120V | 1500 | 200 | CC-2V | 3 5/8" | Box | 500/25 |
| 40 | CA-9 1/2 | Cand. | S3279 | 40CA9 1/2/F | Frosted | 120V | 1500 | 384 | CC-2V | 3 15/16" | Box | 500/25 |
| 60 | CA-10 | Cand. | S3263 | 60CA10/F | Frosted | 120V | 1500 | 672 | CC-2V | 4 1/4" | Box | 500/25 |

decorative incandescent lamps

Bulbs

Candelabra Base



Petite Clear

Clear

Frosted

White

S3345 15 Watt
S3346 25 Watt
S3347 40 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner

S3230 15 Watt
S3282 25 Watt
S3283 40 Watt
S3284 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner

S3291 15 Watt
S3285 25 Watt
S3286 40 Watt
S3287 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner

S3288 25 Watt
S3289 40 Watt
S3290 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 15 | B8 | Cand. | S3345 | 15B8/Petite | Clear | 130V | 2500 | 114 | C7A | 3" | Box | 500/25 |
| 15 | B9 1/2 | Cand. | S3230 | 15B9 1/2 | Clear | 120V | 1500 | 114 | C7A | 3 1/2" | Box | 500/25 |
| 15 | B9 1/2 | Cand. | S3291 | 15B9 1/2/F | Frosted | 120V | 1500 | 114 | C7A | 3 1/2" | Box | 500/25 |
| 25 | B8 | Cand. | S3346 | 25B8/Petite | Clear | 130V | 2500 | 212 | CC-2V | 3" | Box | 500/25 |
| 25 | B9 1/2 | Cand. | S3282 | 25B9 1/2 | Clear | 120V | 1500 | 212 | CC-2V | 3 1/2" | Box | 500/25 |
| 25 | B9 1/2 | Cand. | S3285 | 25B9 1/2/F | Frosted | 120V | 1500 | 212 | CC-2V | 3 1/2" | Box | 500/25 |
| 25 | B9 1/2 | Cand. | S3288 | 25B9 1/2/W | White | 120V | 1500 | 180 | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B8 | Cand. | S3347 | 40B8/Petite | Clear | 130V | 2500 | 384 | CC-2V | 3" | Box | 500/25 |
| 40 | B9 1/2 | Cand. | S3283 | 40B9 1/2 | Clear | 120V | 1500 | 384 | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B9 1/2 | Cand. | S3286 | 40B9 1/2/F | Frosted | 120V | 1500 | 384 | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B9 1/2 | Cand. | S3289 | 40B9 1/2/W | White | 120V | 1500 | 328 | CC-2V | 3 1/2" | Box | 500/25 |
| 60 | B10 | Cand. | S3284 | 60B10 | Clear | 120V | 1500 | 672 | CC-2V | 3 3/4" | Box | 500/25 |
| 60 | B10 | Cand. | S3287 | 60B10/F | Frosted | 120V | 1500 | 672 | CC-2V | 3 3/4" | Box | 500/25 |
| 60 | B10 | Cand. | S3290 | 60B10/W | White | 120V | 1500 | 630 | CC-2V | 3 3/4" | Box | 500/25 |

1500 Hours / 120 Volt

Medium Base



White

S3237 25 Watt
S3238 40 Watt
S3299 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Frosted

S3234 25 Watt
S3235 40 Watt
S3296 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Clear

S3231 25 Watt
S3232 40 Watt
S3293 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B11 | Med. | S3231 | 25B11 | Clear | 120V | 1500 | 210 | CC-2V | 3 7/8" | Box | 500/25 |
| 25 | B11 | Med. | S3234 | 25B11/F | Frosted | 120V | 1500 | 200 | CC-2V | 3 7/8" | Box | 500/25 |
| 25 | B11 | Med. | S3237 | 25B11/W | White | 120V | 1500 | 150 | CC-2V | 3 7/8" | Box | 500/25 |
| 40 | B11 | Med. | S3232 | 40B11 | Clear | 120V | 1500 | 370 | CC-2V | 3 7/8" | Box | 500/25 |
| 40 | B11 | Med. | S3235 | 40B11/F | Frosted | 120V | 1500 | 360 | CC-2V | 3 7/8" | Box | 500/25 |
| 40 | B11 | Med. | S3238 | 40B11/W | White | 120V | 1500 | 330 | CC-2V | 3 7/8" | Box | 500/25 |
| 60 | B11 | Med. | S3293 | 60B11 | Clear | 120V | 1500 | 650 | CC-2V | 3 7/8" | Box | 500/25 |
| 60 | B11 | Med. | S3296 | 60B11/F | Frosted | 120V | 1500 | 640 | CC-2V | 3 7/8" | Box | 500/25 |
| 60 | B11 | Med. | S3299 | 60B11/W | White | 120V | 1500 | 580 | CC-2V | 3 7/8" | Box | 500/25 |

Bulbs

120 Volt / 1500 Hours

Medium Base



Frosted

S3267 25 Watt
S3268 40 Watt
S3269 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner



Clear

S3264 25 Watt
S3265 40 Watt
S3266 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | CA-10 | Med. | S3264 | 25CA10 | Clear | 120V | 1500 | 210 | CC-2V | 4 1/4" | Box | 500/25 |
| 25 | CA-10 | Med. | S3267 | 25CA10/F | Frosted | 120V | 1500 | 200 | CC-2V | 4 1/4" | Box | 500/25 |
| 40 | CA-10 | Med. | S3265 | 40CA10 | Clear | 120V | 1500 | 370 | CC-2V | 4 1/4" | Box | 500/25 |
| 40 | CA-10 | Med. | S3268 | 40CA10/F | Frosted | 120V | 1500 | 360 | CC-2V | 4 1/4" | Box | 500/25 |
| 60 | CA-10 | Med. | S3266 | 60CA10 | Clear | 120V | 1500 | 650 | CC-2V | 4 1/4" | Box | 500/25 |
| 60 | CA-10 | Med. | S3269 | 60CA10/F | Frosted | 120V | 1500 | 640 | CC-2V | 4 1/4" | Box | 500/25 |

decorative incandescent lamps

2500 Hours / 130 Volt

Candelabra Base



A3677 15 Watt
*Packing: Indiv. Boxed
500/Master, 25/Inner*

A3678 25 Watt
*Packing: Indiv. Boxed
500/Master, 25/Inner*

A3679 40 Watt
*Packing: Indiv. Boxed
500/Master, 25/Inner*

A3663 60 Watt
*Packing: Indiv. Boxed
500/Master, 25/Inner*

Shown Actual Size

| Watts | Bulb Type | Base | Satco | | Finish | Volts | Avg. Rated | | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|--------------|-------------|---------|-------|------------|--------|----------|----------|------------|-----------------------|
| | | | Order No. | Lamp Code | | | Hours | Lumens | | | | |
| 15 | CA-8 | Cand. | A3677 | 15CA8/F | Frosted | 130V | 2500 | 90 | C-7A | 3 5/8" | Box | 500/25 |
| 25 | CA-8 | Cand. | A3678 | 25CA8/F | Frosted | 130V | 2500 | 200 | CC-2V | 3 5/8" | Box | 500/25 |
| 40 | CA-9 1/2 | Cand. | A3679 | 40CA9 1/2/F | Frosted | 130V | 2500 | 350 | CC-2V | 3 15/16" | Box | 500/25 |
| 60 | CA-10 | Cand. | A3663 | 60CA10/F | Frosted | 130V | 2500 | 635 | CC-2V | 4 1/4" | Box | 500/25 |

decorative incandescent lamps

Bulbs

130 Volt / 2500 Hours

Candelabra Base



Clear

A3673 15 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Clear

A3674 25 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Clear

A3675 40 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Clear

A3662 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 15 | CA-8 | Cand. | A3673 | 15CA8 | Clear | 130V | 2500 | 95 | C-7A | 3 5/8" | Box | 500/25 |
| 25 | CA-8 | Cand. | A3674 | 25CA8 | Clear | 130V | 2500 | 210 | CC-2V | 3 5/8" | Box | 500/25 |
| 40 | CA-9 1/2 | Cand. | A3675 | 40CA9 1/2 | Clear | 130V | 2500 | 370 | CC-2V | 3 15/16" | Box | 500/25 |
| 60 | CA-10 | Cand. | A3662 | 60CA10 | Clear | 130V | 2500 | 642 | CC-2V | 4 1/4" | Box | 500/25 |

decorative incandescent lamps

2500 Hours / 130 Volt

Candelabra Base



A3620 15 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

A3682 25 Watt
A3683 40 Watt
A3684 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

A3685 25 Watt
A3686 40 Watt
A3687 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

A3688 25 Watt
A3689 40 Watt
A3690 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 15 | B9 1/2 | Cand. | A3620 | 15B9 1/2 | Clear | 130V | 2500 | 95 | CC-2V | 3 1/2" | Box | 500/25 |
| 25 | B9 1/2 | Cand. | A3682 | 25B9 1/2 | Clear | 130V | 2500 | 193 | CC-2V | 3 1/2" | Box | 500/25 |
| 25 | B9 1/2 | Cand. | A3685 | 25B9 1/2/F | Frosted | 130V | 2500 | 193 | CC-2V | 3 1/2" | Box | 500/25 |
| 25 | B9 1/2 | Cand. | A3688 | 25B9 1/2/W | White | 130V | 2500 | 163 | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B9 1/2 | Cand. | A3683 | 40B9 1/2 | Clear | 130V | 2500 | 384 | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B9 1/2 | Cand. | A3686 | 40B9 1/2/F | Frosted | 130V | 2500 | 384 | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B9 1/2 | Cand. | A3689 | 40B9 1/2/W | White | 130V | 2500 | 328 | CC-2V | 3 1/2" | Box | 500/25 |
| 60 | B10 | Cand. | A3684 | 60B10 | Clear | 130V | 2500 | 642 | CC-2V | 3 3/4" | Box | 500/25 |
| 60 | B10 | Cand. | A3687 | 60B10/F | Frosted | 130V | 2500 | 642 | CC-2V | 3 3/4" | Box | 500/25 |
| 60 | B10 | Cand. | A3690 | 60B10/W | White | 130V | 2500 | 564 | CC-2V | 3 3/4" | Box | 500/25 |

decorative incandescent lamps

Bulbs

130 Volt / 2500 Hours

Medium Base



White

A3637 25 Watt
A3638 40 Watt
A3699 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner



Frosted

A3634 25 Watt
A3635 40 Watt
A3696 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner



Clear

A3631 25 Watt
A3632 40 Watt
A3693 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B11 | Med. | A3631 | 25B11 | Clear | 130V | 2500 | 210 | CC-2V | 3 7/8" | Box | 500/25 |
| 25 | B11 | Med. | A3634 | 25B11/F | Frosted | 130V | 2500 | 200 | CC-2V | 3 7/8" | Box | 500/25 |
| 25 | B11 | Med. | A3637 | 25B11/W | White | 130V | 2500 | 160 | CC-2V | 3 7/8" | Box | 500/25 |
| 40 | B11 | Med. | A3632 | 40B11 | Clear | 130V | 2500 | 370 | CC-2V | 3 7/8" | Box | 500/25 |
| 40 | B11 | Med. | A3635 | 40B11/F | Frosted | 130V | 2500 | 360 | CC-2V | 3 7/8" | Box | 500/25 |
| 40 | B11 | Med. | A3638 | 40B11/W | White | 130V | 2500 | 320 | CC-2V | 3 7/8" | Box | 500/25 |
| 60 | B11 | Med. | A3693 | 60B11 | Clear | 130V | 2500 | 650 | CC-2V | 3 7/8" | Box | 500/25 |
| 60 | B11 | Med. | A3696 | 60B11/F | Frosted | 130V | 2500 | 640 | CC-2V | 3 7/8" | Box | 500/25 |
| 60 | B11 | Med. | A3699 | 60B11/W | White | 130V | 2500 | 550 | CC-2V | 3 7/8" | Box | 500/25 |

2500 Hours / 130 Volt

Medium Base



Clear

A3664 25 Watt
A3665 40 Watt
A3666 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Frosted

A3667 25 Watt
A3668 40 Watt
A3669 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | CA-10 | Med. | A3664 | 25CA10 | Clear | 130V | 2500 | 210 | CC-2V | 4 1/4" | Box | 500/25 |
| 25 | CA-10 | Med. | A3667 | 25CA10/F | Frosted | 130V | 2500 | 200 | CC-2V | 4 1/4" | Box | 500/25 |
| 40 | CA-10 | Med. | A3665 | 40CA10 | Clear | 130V | 2500 | 370 | CC-2V | 4 1/4" | Box | 500/25 |
| 40 | CA-10 | Med. | A3668 | 40CA10/F | Frosted | 130V | 2500 | 360 | CC-2V | 4 1/4" | Box | 500/25 |
| 60 | CA-10 | Med. | A3666 | 60CA10 | Clear | 130V | 2500 | 650 | CC-2V | 4 1/4" | Box | 500/25 |
| 60 | CA-10 | Med. | A3669 | 60CA10/F | Frosted | 130V | 2500 | 640 | CC-2V | 4 1/4" | Box | 500/25 |

decorative incandescent lamps

Decorative bulbs

decorative incandescent lamps

Torpedo
Euro Base E14

Specialty
Product



Clear
S3390 25 Watt
S3391 40 Watt
S3392 60 Watt



Frosted
S3380 25 Watt
S3381 40 Watt
S3382 60 Watt

1500 Hrs. Average Life (120 Volt)
Packing: Individually Boxed, 500/Master, 25/Inner

Petite Turn-Tip 7½ Watt
Candelabra Base



Clear
S3241 7½ Watt



Frosted
S3242 7½ Watt



**Frosted/
Yellow Tip**
S3243 7½ Watt

1500 Hrs. Average Life (120 Volt)
Packing: Indiv. Boxed, 2000/Master, 50/Inner

7½ Watt
"SHOWROOM"
BULB

Candelabra Base
3000 Hrs. Average Life
(120 Volt)
Clear

S4994 Torpedo
S4988 Turn Tip

Packing: Individually Boxed
500/Master, 25/Inner

**Full Size/
Low Wattage**
Perfect for
Fixture Displays



Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------------|-----------------|------------|--------------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 7½ | CA-5 | Cand. | S3241 | 7½CA5 | Clear | 120V | 1500 | 40 | C-7A | 2 7/8" | Box | 2000/50 |
| 7½ | CA-5 | Cand. | S3242 | 7½CA5/F | Frosted | 120V | 1500 | 35 | C-7A | 2 7/8" | Box | 2000/50 |
| 7½ | CA-5 | Cand. | S3243 | 7½CA5/FY | Frost. Yell. | 120V | 1500 | 35 | C-7A | 2 7/8" | Box | 2000/50 |
| 7½ | B9½ | Cand. | S4994 | 7½B9½ | Clear | 120V | 3000 | 37 | C-7A | 3 1/2" | Box | 500/25 |
| 7½ | C9½ | Cand. | S4988 | 7½C9½ | Clear | 120V | 3000 | 37 | C-7A | 3 1/2" | Box | 500/25 |
| 25 | B-9½ | Euro. Base | S3390 | 25B9 1/2 | Clear | 120V | 1500 | 210 | CC-2V | 3 1/2" | Box | 500/25 |
| 25 | B-9½ | Euro. Base | S3380 | 25B9 1/2/F | Frosted | 120V | 1500 | 200 | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B-9½ | Euro. Base | S3391 | 40B9 1/2 | Clear | 120V | 1500 | 370 | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B-9½ | Euro. Base | S3381 | 40B9 1/2/F | Frosted | 120V | 1500 | 360 | CC-2V | 3 1/2" | Box | 500/25 |
| 60 | B10 | Euro. Base | S3392 | 60B10 | Clear | 120V | 1500 | 650 | CC-2V | 3 3/4" | Box | 500/25 |
| 60 | B10 | Euro. Base | S3382 | 60B10/F | Frosted | 120V | 1500 | 640 | CC-2V | 3 3/4" | Box | 500/25 |



Not Shown Actual Size



Silicone

S4520 5 Watt
Packing: Card/2
144/Master, 12/Inner



12V Clear

S3866 7 Watt
S3867 15 Watt
S3868 25 Watt
S3869 25 Watt
Packing: 500/Master,
25/Inner

decorative incandescent lamps

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|---------------|----------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 7 | CA-10 | Cand. | S3866 | 7CA10/CL/12V | Clear | 12V | 1500 | 65 | CC-2V | 4 1/4" | Box | 500/25 |
| 15 | CA-10 | Cand. | S3867 | 15CA10/CL/12V | Frosted | 12V | 1500 | 150 | CC-2V | 4 1/4" | Box | 500/25 |
| 25 | CA-10 | Cand. | S3868 | 25CA10/CL/12V | Clear | 12V | 1500 | 250 | CC-2V | 4 1/4" | Box | 500/25 |
| 25 | CA-10 | Med. | S3869 | 25CA10/CL/12V | Clear | 12V | 1500 | 250 | CC-2V | 4 1/4" | Box | 500/25 |
| 5 | C-7 | Cand. | S4520 | 5C7 | Silicone | 120V | 1000 | 10 | C-7A | 2 1/2+" | 2/Card | 144/12 |

Bulbs

120 Volt / 1500 Hours

F10 Candelabra Base

Not Shown Actual Size



Clear

S3360 15 Watt
S3371 25 Watt



White

S3361 15 Watt
S3372 25 Watt



Aurora

S3373 25 Watt



Amber

S3374 25 Watt

Packing: Indiv. Boxed, 500/Master, 25/Inner

F15

Medium Base



- S3363** 25 Watt Clear
- S3367** 40 Watt Clear
- S3364** 25 Watt White
- S3368** 40 Watt White
- S3365** 25 Watt Aurora
- S3369** 40 Watt Aurora
- S3366** 25 Watt Amber
- S3370** 40 Watt Amber

Packing: Indiv. Boxed
300/Master, 25/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 15 | F10 | Cand. | S3360 | 15F10 | Clear | 120V | 1500 | 110 | C-7A | 3 1/16" | Box | 500/25 |
| 15 | F10 | Cand. | S3361 | 15F10/W | White | 120V | 1500 | 90 | C-7A | 3 1/16" | Box | 500/25 |
| 25 | F10 | Cand. | S3371 | 25F10 | Clear | 120V | 1500 | 195 | C-7A | 3 1/16" | Box | 500/25 |
| 25 | F10 | Cand. | S3372 | 25F10/W | White | 120V | 1500 | 185 | C-7A | 3 1/16" | Box | 500/25 |
| 25 | F10 | Cand. | S3373 | 25F10/AU | Aurora | 120V | 1500 | 190 | C-7A | 3 1/16" | Box | 500/25 |
| 25 | F10 | Cand. | S3374 | 25F10/A | Amber | 120V | 1500 | n/a | C-7A | 3 1/16" | Box | 500/25 |
| 25 | F15 | Med. | S3363 | 25F15 | Clear | 120V | 1500 | 225 | CC-9 | 4 1/2" | Box | 300/25 |
| 25 | F15 | Med. | S3364 | 25F15/W | White | 120V | 1500 | 195 | CC-9 | 4 1/2" | Box | 300/25 |
| 25 | F15 | Med. | S3365 | 25F15/AU | Aurora | 120V | 1500 | 200 | CC-9 | 4 1/2" | Box | 300/25 |
| 25 | F15 | Med. | S3366 | 25F15/A | Amber | 120V | 1500 | n/a | CC-9 | 4 1/2" | Box | 300/25 |
| 40 | F15 | Med. | S3367 | 40F15 | Clear | 120V | 1500 | 420 | CC-9 | 4 1/2" | Box | 300/25 |
| 40 | F15 | Med. | S3368 | 40F15/W | White | 120V | 1500 | 372 | CC-9 | 4 1/2" | Box | 300/25 |
| 40 | F15 | Med. | S3369 | 40F15/AU | Aurora | 120V | 1500 | 420 | CC-9 | 4 1/2" | Box | 300/25 |
| 40 | F15 | Med. | S3370 | 40F15/A | Amber | 120V | 1500 | n/a | CC-9 | 4 1/2" | Box | 300/25 |

decorative incandescent lamps



Krypton decorative bulbs create a brilliant sparkle, similar to the look of halogen. Excellent for use in crystal chandeliers and fixtures with decorative glassware.

Additionally, Krypton bulbs last longer than conventional lamps and maintain their lumen output during the full course of their life.

2500 Hours **Bulbs**

Not Shown Actual Size



G16 1/2

Torpedo

Flame

Torpedo

Clear

- S4471** 25 Watt
- S4472** 40 Watt
- S4473** 60 Watt

*Packing: Indiv. Boxed
500/Master, 25/Inner*

Clear

- S4995** 25Watt
- S4996** 40 Watt
- S4997** 60 Watt

*Packing: Indiv. Boxed
500/Master, 25/Inner*

Clear

- S4465** 25 Watt
- S4466** 40 Watt
- S4467** 60 Watt

*Packing: Indiv. Boxed
500/Master, 25/Inner*

Clear

- S4468** 25Watt
- S4469** 40 Watt
- S4470** 60 Watt

*Packing: Indiv. Boxed
500/Master, 25/Inner*

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-------------|--------|-------|------------------|--------|----------|----------|-----------|-----------------------|
| 25 | B9 1/2 | Cand. | S4995 | KR25B9 1/2 | Clear | 120V | 2500 | 212 | CC-2V | 3 7/8" | Box | 500/25 |
| 25 | CA-9 1/2 | Cand. | S4465 | KR25CA9 1/2 | Clear | 120V | 2500 | 212 | CC-2V | 3 15/16" | Box | 500/25 |
| 25 | B11 | Med. | S4468 | KR25B11 | Clear | 120V | 2500 | 212 | CC-2V | 3 7/8" | Box | 500/25 |
| 25 | G16 1/2 | Cand. | S4471 | KR25G16 1/2 | Clear | 120V | 2500 | 212 | CC-2V | 3" | Box | 500/25 |
| 40 | B-9 1/2 | Cand. | S4996 | KR40B9 1/2 | Clear | 120V | 2500 | 380 | CC-2V | 3 7/8" | Box | 500/25 |
| 40 | CA-9 1/2 | Cand. | S4466 | KR40CA9 1/2 | Clear | 120V | 2500 | 380 | CC-2V | 3 15/16" | Box | 500/25 |
| 40 | B11 | Med. | S4469 | KR40B11 | Clear | 120V | 2500 | 380 | CC-2V | 3 7/8" | Box | 500/25 |
| 40 | G16 1/2 | Cand. | S4472 | KR40G16 1/2 | Clear | 120V | 2500 | 380 | CC-2V | 3" | Box | 500/25 |
| 60 | B10 | Cand. | S4997 | KR60B11 | Clear | 120V | 2500 | 720 | CC-2V | 3 7/8" | Box | 500/25 |
| 60 | CA-10 | Cand. | S4467 | KR60CA-10 | Clear | 120V | 2500 | 720 | CC-2V | 4 1/4" | Box | 500/25 |
| 60 | B11 | Med. | S4470 | KR60B11 | Clear | 120V | 2500 | 720 | CC-2V | 3 7/8" | Box | 500/25 |
| 60 | G16 1/2 | Cand. | S4473 | KR60G16 1/2 | Clear | 120V | 2500 | 720 | CC-2V | 3" | Box | 500/25 |

decorative incandescent lamps

Bulbs

120 Volt / 4000 Hours

decorative incandescent lamps



C15

Amber

Medium Base

S3416 40 Watt

Packing: Individually Boxed
300/Master, 25/Inner



C15

Satin

Medium Base

S3413 25 Watt

S3414 40 Watt

S3415 60 Watt

Packing: Individually Boxed
300/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | C15 | Med. | S3413 | 25C15 | Satin | 120V | 4000 | 160 | C-9 | 4 1/2" | Box | 300/25 |
| 40 | C15 | Med. | S3414 | 40C15 | Satin | 120V | 4000 | 316 | C-9 | 4 1/2" | Box | 300/25 |
| 40 | C15 | Med. | S3416 | 40C15/A | Amber | 120V | 4000 | n/a | C-9 | 4 1/2" | Box | 300/25 |
| 60 | C15 | Med. | S3415 | 60C15 | Satin | 120V | 4000 | 606 | C-9 | 4 1/2" | Box | 300/25 |

4000 Hours / 120Volts

Bulbs



C11

C11

Satin

Candelabra Base

S3403 25 Watt

S3404 40 Watt

S3405 60 Watt

Packing: Individually Boxed
500/Master, 25/Inner

Amber

Candelabra Base

S3406 25 Watt

Packing: Individually Boxed
500/Master, 25/Inner

Satco-Escent[®]
bulbs simulate the feel and charm of an old style gas light. The unique silk like threading wraps around the bulbs and enhances the image of the filament into an elongated glow. Perfect for use in outdoor lanterns and exposed bulb chandeliers.

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated | | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|------------|-------|--------|----------|--------|------------|-----------------------|
| | | | | | | Volts | Hours | | | | | |
| 25 | C11 | Cand. | S3403 | 25C11 | Satin | 120V | 4000 | 160 | C-7A | 4" | Box | 500/25 |
| 25 | C11 | Cand. | S3406 | 25C11/A | Amber | 120V | 4000 | n/a | C-7A | 4" | Box | 500/25 |
| 40 | C11 | Cand. | S3404 | 40C11 | Satin | 120V | 4000 | 316 | C-7A | 4" | Box | 500/25 |
| 60 | C11 | Cand. | S3405 | 60C11 | Satin | 120V | 4000 | 606 | C-7A | 4" | Box | 500/25 |

decorative incandescent lamps

Bulbs

120 Volt / 1000 Hours

decorative incandescent lamps



Candelabra Base

S3661 3 Watt



Candelabra Base

S3656 3 Watt



Candelabra Base

S3659 3 Watt



Medium Base

S3657 3 Watt



Medium Base

S3660 3 Watt

Packing: Individually Boxed
500/Master, 25/Inner

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|--------------|--------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 3 | CA-5 1/2 | Cand. | S3661 | 3CA5 1/2/FLK | Clear | 120V | 1000 | n/a | Flicker | 3 1/4" | Box | 500/25 |
| 3 | CA-8 | Cand. | S3659 | 3CA8/FLK | Clear | 120V | 1000 | n/a | Flicker | 3 7/8" | Box | 500/25 |
| 3 | B-9 1/2 | Cand. | S3656 | 3B9 1/2/FLK | Clear | 120V | 1000 | n/a | Flicker | 3 1/2" | Box | 500/25 |
| 3 | CA-10 | Med. | S3657 | 3CA10/FLK | Clear | 120V | 1000 | n/a | Flicker | 4 1/16" | Box | 500/25 |
| 3 | CA-9 | Med. | S3660 | 3CA9/FLK | Clear | 120V | 1000 | n/a | Flicker | 4 9/16" | Box | 500/25 |

1500 Hours / 120 Volt

Candelabra Base



Clear



Frosted



Aurora

Candelabra Base
S3744 25 Watt
S3745 40 Watt
 Packing: Card/2
 120 Master, 12 Inner

Candelabra Base
S3746 25 Watt
S3747 40 Watt
 Packing: Card/2
 120 Master, 12 Inner

Candelabra Base
S3748 25 Watt
S3749 40 Watt
 Packing: Card/2
 120 Master, 12 Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Volts | Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|---------------|---------|------------------|-------|--------|----------|----------|------------|-----------------------|
| 25 | HX-10 1/2 | Cand. | S3744 | 25HX10 1/2 | Clear | 120V | 1500 | 175 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 25 | HX-10 1/2 | Cand. | S3746 | 25HX10 1/2/F | Frosted | 120V | 1500 | 175 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 25 | HX-10 1/2 | Cand. | S3748 | 25HX10 1/2/AU | Aurora | 120V | 1500 | 175 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 40 | HX-10 1/2 | Cand. | S3745 | 40HX10 1/2 | Clear | 120V | 1500 | 360 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 40 | HX-10 1/2 | Cand. | S3747 | 40HX10 1/2/F | Frosted | 120V | 1500 | 360 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 40 | HX-10 1/2 | Cand. | S3749 | 40HX10 1/2/AU | Aurora | 120V | 1500 | 360 | C-7A | 4 15/16" | Card/2 | 120/12 |

decorative incandescent lamps

Torpedo

120 Volt / 1500 Hours



Amber
Candelabra Base

S3813 25 Watt
S3818 40 Watt
S3819 60 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner



Red
Candelabra Base

S3219 25 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner



Blue
Candelabra Base

S3218 25 Watt
 Packing: Indiv. Boxed
 500/Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B-91/2 | Cand. | S3218 | 25B91/2/B | Blue | 120V | 1500 | n/a | CC-2V | 3 1/2" | Box | 500/25 |
| 25 | B-91/2 | Cand. | S3219 | 25B91/2/R | Red | 120V | 1500 | n/a | CC-2V | 3 1/2" | Box | 500/25 |
| 25 | B-91/2 | Cand. | S3813 | 25B91/2/A | Amber | 120V | 1500 | n/a | CC-2V | 3 1/2" | Box | 500/25 |
| 40 | B-91/2 | Cand. | S3818 | 40B91/2/A | Amber | 120V | 1500 | n/a | CC-2V | 3 1/2" | Box | 500/25 |
| 60 | B-91/2 | Cand. | S3819 | 60B91/2/A | Amber | 120V | 1500 | n/a | CC-2V | 3 1/2" | Box | 500/25 |

decorative incandescent lamps

Night



Light bulbs

Brass Base

Candelabra Base



7C7

Candelabra Base
(120 Volt)

S3691 7 Watt Clear

S3692 7 Watt White

Packing: Bulk
2000/Master, 25/Box

Shown Actual Size



4C7

Candelabra Base (120 Volt)

S3680 4 Watt Clear

S3681 4 Watt White

Packing: Bulk
2000/Master, 50/Box

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 4 | C7 | Cand. | S3680 | 4C7 | Clear | 120V | 3000 | 16 | C-7A | 2 1/8" | Bulk | 2000/50 |
| 4 | C7 | Cand. | S3681 | 4C7/W | White | 120V | 3000 | 8 | C-7A | 2 1/8" | Bulk | 2000/50 |
| 7 | C7 | Cand. | S3691 | 7C7 | Clear | 120V | 3000 | 35 | C-7A | 2 1/8" | Bulk | 2000/25 |
| 7 | C7 | Cand. | S3692 | 7C7/W | White | 120V | 3000 | 20 | C-7A | 2 1/8" | Bulk | 2000/25 |

general service lamps

2500 Hours



7 1/2 S11

Medium Base
2500 Hrs. Average Life
(120 Volt)

- S3606** 7 1/2 Watt Clear
- S3607** 7 1/2 Watt Glossy White
- S3608** 7 1/2 Watt Ceramic Blue
- S3609** 7 1/2 Watt Ceramic Green
- S3610** 7 1/2 Watt Ceramic Orange
- S3611** 7 1/2 Watt Ceramic Red

Packing: Individually Boxed
1000/Master, 25/Inner



11 S14

Medium Base
2500 Hrs. Average Life
(130 Volt)

- S3965** 11 Watt Clear
- S3960** 11 Watt Ceramic Yellow
- S3961** 11 Watt Ceramic Red
- S3962** 11 Watt Ceramic Green
- S3963** 11 Watt Ceramic Blue
- S3964** 11 Watt Ceramic Orange
- S3966** 11 Watt Frosted

Packing: 4 Pack Sleeve, 120/Master



Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-------------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 7 1/2 | S11 | Med. | S3606 | 7 1/2 S11 | Clear | 120V | 2500 | 40 | C-7A | 2 1/4" | Sleeve | 1000/25 |
| 7 1/2 | S11 | Med. | S3607 | 7 1/2 S11/W | White | 120V | 2500 | 25 | C-7A | 2 1/4" | Sleeve | 1000/25 |
| 7 1/2 | S11 | Med. | S3608 | 7 1/2 S11/B | Blue | 120V | 2500 | n/a | C-7A | 2 1/4" | Sleeve | 1000/25 |
| 7 1/2 | S11 | Med. | S3609 | 7 1/2 S11/G | Green | 120V | 2500 | n/a | C-7A | 2 1/4" | Sleeve | 1000/25 |
| 7 1/2 | S11 | Med. | S3610 | 7 1/2 S11/O | Orange | 120V | 2500 | n/a | C-7A | 2 1/4" | Sleeve | 1000/25 |
| 7 1/2 | S11 | Med. | S3611 | 7 1/2 S11/R | Red | 120V | 2500 | n/a | C-7A | 2 1/4" | Sleeve | 1000/25 |
| 11 | S14 | Med. | S3965 | 11 S14 | Clear | 130V | 2500 | 80 | CC-9 | 3 1/2" | Sleeve | 120/4 |
| 11 | S14 | Med. | S3966 | 11 S14/F | Frost. | 130V | 2500 | 65 | CC-9 | 3 1/2" | Sleeve | 120/4 |
| 11 | S14 | Med. | S3963 | 11 S14/B | Blue | 130V | 2500 | n/a | CC-9 | 3 1/2" | Sleeve | 120/4 |
| 11 | S14 | Med. | S3962 | 11 S14/G | Green | 130V | 2500 | n/a | CC-9 | 3 1/2" | Sleeve | 120/4 |
| 11 | S14 | Med. | S3964 | 11 S14/O | Orange | 130V | 2500 | n/a | CC-9 | 3 1/2" | Sleeve | 120/4 |
| 11 | S14 | Med. | S3961 | 11 S14/R | Red | 130V | 2500 | n/a | CC-9 | 3 1/2" | Sleeve | 120/4 |
| 11 | S14 | Med. | S3960 | 11 S14/Y | Yellow | 130V | 2500 | n/a | CC-9 | 3 1/2" | Sleeve | 120/4 |

T10 Tubular *Brass Base*



Bulbs

120 Volt / 1000 Hours

Medium Base

general service lamps



Clear

*Medium Base
(120 Volt)*

- S3250** 25 Watt
- S3252** 40 Watt
- S3896** 60 Watt

*Packing: Individually Boxed
500/Master, 25/Inner*



Frosted

*Medium Base
(120 Volt)*

- S3251** 25 Watt
- S3253** 40 Watt
- S3899** 60 Watt

*Packing: Individually Boxed
500/Master, 25/Inner*

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 25 | T10 | Med. | S3250 | 25T10 | Clear | 120V | 1000 | 210 | C-5V | 5 3/16" | Box | 500/25 |
| 25 | T10 | Med. | S3251 | 25T10/F | Frosted | 120V | 1000 | 200 | C-5V | 5 3/16" | Box | 500/25 |
| 40 | T10 | Med. | S3252 | 40T10 | Clear | 120V | 1000 | 300 | C-5V | 5 3/16" | Box | 500/25 |
| 40 | T10 | Med. | S3253 | 40T10/F | Frosted | 120V | 1000 | 290 | C-5V | 5 3/16" | Box | 500/25 |
| 60 | T10 | Med. | S3896 | 60T10 | Clear | 120V | 1000 | 490 | C-5V | 5 3/16" | Box | 500/25 |
| 60 | T10 | Med. | S3899 | 60T10/F | Frosted | 120V | 1000 | 480 | C-5V | 5 3/16" | Box | 500/25 |

1500 Hours / 130 Volt

D.C. Bayonet Base

Shown Actual Size



Clear



Frosted

D.C. Bayonet Base
(130 Volt)

S3297 20 Watt
S3248 25 Watt

Packing: Individually Boxed
500/Master, 25/Inner

D.C. Bayonet Base
(130 Volt)

S3298 20 Watt
S3249 25 Watt

Packing: Individually Boxed
500/Master, 25/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|--------------------------------|--------|-----------------|---------------------------------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 20 | T6 ¹ / ₂ | DC BAY | S3297 | 20T6 ¹ / ₂ DC | Clear | 130V | 1500 | 150 | C-8 | 5 3/8" | Box | 500/25 |
| 20 | T6 ¹ / ₂ | DC BAY | S3298 | 20T6 ¹ / ₂ DC/F | Frosted | 130V | 1500 | 140 | C-8 | 5 3/8" | Box | 500/25 |
| 25 | T6 ¹ / ₂ | DC BAY | S3248 | 25T6 ¹ / ₂ DC | Clear | 130V | 1500 | 180 | C-8 | 5 3/8" | Box | 500/25 |
| 25 | T6 ¹ / ₂ | DC BAY | S3249 | 25T6 ¹ / ₂ DC/F | Frosted | 130V | 1500 | 170 | C-8 | 5 3/8" | Box | 500/25 |



T6¹/₂ Tubular *Brass Base*



Bulbs

130 Volt / 1500 Hours

Intermediate Base

Shown Actual Size



Clear



Frosted

*Intermediate Base
(130 Volt)*

- S3280** 20 Watt Clear
- S3222** 25 Watt Clear
- S3224** 40 Watt Clear

*Packing: Individually Boxed
500/Master, 25/Inner*

*Intermediate Base
(130 Volt)*

- S3281** 20 Watt Frosted
- S3223** 25 Watt Frosted
- S3225** 40 Watt Frosted

*Packing: Individually Boxed
500/Master, 25/Inner*

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 20 | T61/2 | Int. | S3280 | 20T61/2N | Clear | 130V | 1500 | 150 | C-8 | 5 3/8" | Box | 500/25 |
| 20 | T61/2 | Int. | S3281 | 20T61/2N/IF | Frosted | 130V | 1500 | 140 | C-8 | 5 3/8" | Box | 500/25 |
| 25 | T61/2 | Int. | S3222 | 25T61/2N | Clear | 130V | 1500 | 180 | C-8 | 5 3/8" | Box | 500/25 |
| 25 | T61/2 | Int. | S3223 | 25T61/2N/IF | Frosted | 130V | 1500 | 170 | C-8 | 5 3/8" | Box | 500/25 |
| 40 | T61/2 | Int. | S3224 | 40T61/2N | Clear | 130V | 1500 | 350 | C-8 | 5 3/8" | Box | 500/25 |
| 40 | T61/2 | Int. | S3225 | 40T61/2N/IF | Frosted | 130V | 1500 | 340 | C-8 | 5 3/8" | Box | 500/25 |

general service lamps



Shown Actual Size



Intermediate Base
115-125 Volt

S3621 10 Watt
Dom. Code #10S11N

S3628 15 Watt
Dom. Code #15S11N

S3630 25 Watt
Dom. Code #25S11N

S3629 40 Watt
Dom. Code #40S11N

Packing: Individually Boxed
600/Master, 10/Inner



S3624 24 Watt/15CP
SC Bayonet Base/6-8V
Dom. Code #1133

Packing: Individually Boxed
600/Master, 10/Inner



S3623 12 Watt/15CP
SC Bayonet Base/12-16V
Dom. Code #93

Packing: Individually Boxed
600/Master, 10/Inner



S1383 20 Watt/20 CP
S.C. Bayonet Base 13 Volt

Packing: Individually Boxed
600/Master, 10/Inner



S3622 10 Watt
Intermediate Base/115-125V
Dom. Code #10S11N/F

Packing: Individually Boxed
600/Master, 10/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|----------|-----------------|---------------|-----------|----------|------------------|--------|----------|--------|------------|-----------------------|
| 12 | S8 | S.C.BAY. | S3623 | 12S8/93 | Clear | 12-16V | 200 | 190 | C-6 | 2 " | Box | 600/10 |
| 10 | S11 | Int. | S3621 | 10S11/N | Clear | 115/125V | 1500 | 80 | C-7A | 2 3/8" | Box | 600/10 |
| 10 | S11 | Int. | S3622 | 10S11N/F | Frosted | 115/125V | 1500 | 80 | CC-2V | 2 3/8" | Box | 600/10 |
| 15 | S11 | Int. | S3628 | 15S11/N | Clear | 115/125V | 1500 | 100 | C-7A | 2 3/8" | Box | 600/10 |
| 25 | S11 | Int. | S3630 | 25S11/N | Clear | 115/125V | 1500 | 210 | CC-2V | 2 3/8" | Box | 600/10 |
| 40 | S11 | Int. | S3629 | 40S11/N | Clear | 115/125V | 1500 | 370 | CC-2V | 2 3/8" | Box | 600/10 |
| 24 | RP11 | S.C.BAY. | S3624 | 24RP11/1133 | Clear | 6/8V | 300 | 400 | C-6 | 2 1/4" | Box | 600/10 |
| 20 | R-11 1/2 | S.C.BAY. | S1383 | 20R111/2/1383 | Frosted | 13V | 600 | 200 | C-6 | 2 1/2" | Box | 600/10 |
| 20 | R-11 1/2 | S.C.BAY. | S1383/TF | 20R111/2/1383 | Shtr Prof | 13V | 600 | 200 | C-6 | 2 1/2" | Box | 600/10 |

Bulbs *Shown Actual Size*

2500 Hours



Indicator Bulb
S3911 15 Watt
 Int. Base/130 Volt
 Dom. Code #15T7/N



Appliance Bulb
S3905 15 Watt
 Cand. Base/130 Volt
 Dom. Code #15T7C



Appliance Bulb
S3908 25 Watt
 Int. Base/130 Volt
 Dom. Code #25T8N



Indicator Bulb
S3907 25 Watt
 Cand. Base/130 Volt
 Dom. Code #25T8C



Indicator Bulb
S3906 15 Watt
 D.C. Bay. Base/130 Volt
 Dom. Code #15T7/DC



Indicator Bulb
S3909 25 Watt
 D.C. Bay. Base/130 Volt
 Dom. Code #25T8DC



Microwave Bulb
S3917 40 Watt
 Int. Base/130 Volt
 Dom. Code #40T8N
 Packing: 1/Card
 120/Master, 12/Inner

Packing: 10 Pack Sleeve
 120/Master, 10/Inner

Appliance • Indicator • Switchboard • Night Light

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 15 | T7 | Int. | S3911 | 15T7/N | Clear | 130V | 2500 | 95 | C-5A | 2 1/4" | Sleeve | 120/10 |
| 15 | T7 | Cand. | S3905 | 15T7 | Clear | 130V | 2500 | 95 | C-5A | 2 1/4" | Sleeve | 120/10 |
| 15 | T7 | DC Bayonet | S3906 | 15T7/DC | Clear | 130V | 2500 | 95 | C-5A | 2 1/4" | Sleeve | 120/10 |
| 25 | T8 | Cand. | S3907 | 25T8 | Clear | 130V | 2500 | 190 | C-5A | 2 5/8" | Sleeve | 120/10 |
| 25 | T8 | Int. | S3908 | 25T8/N | Clear | 130V | 2500 | 190 | C-5A | 2 5/8" | Sleeve | 120/10 |
| 25 | T8 | DC Bayonet | S3909 | 25T8/DC | Clear | 130V | 2500 | 190 | C-5A | 2 5/8" | Sleeve | 120/10 |
| 40 | T8 | Int. | S3917 | 40T8N | Clear | 130V | 2500 | 370 | CC-2V | 2 5/8" | 1/Card | 120/12 |

general service lamps

2500 Hours

Shown Actual Size



Appliance Bulb
S3901 6 Watt
 D.C. Bay. Base
 130 Volt
 Dom. Code #6S6DC



Indicator Bulb
S3900 6 Watt
 Cand. Base
 130 Volt
 Dom. Code #6S6

- Appliance
- Indicator
- Switchboard
- Night Light
- Picture Light



Appliance Bulb
S3904 10 Watt
 D.C. Bay. Base
 130 Volt
 Dom. Code #10C7DC



Night Light
S3902 7 Watt
 Cand. Base/130 Volt
 Dom. Code #7C7
S3903 10 Watt
 Cand. Base/130 Volt
 Dom. Code #10C7



Switchboard Bulb
S3910 15 Watt
 Cand. Base/130 Volt
 Dom. Code #15T6
S3912 15 Watt
 Cand. Base/145 Volt
 Dom. Code #15T6
S3315 15 Watt
 Cand. Base/120 Volt
 Dom. Code #15T6/F

Packing: 10 Pack Sleeve
 120/Master, 10/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------------|-----------------|-----------|--------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 6 | S6 | Cand. | S3900 | 6S6 | Clear | 130V | 2500 | 30 | C-7A | 1 7/8" | Sleeve | 120/10 |
| 6 | S6 | DC Bayonet | S3901 | 6S6/DC | Clear | 130V | 2500 | 30 | C-7A | 1 7/8" | Sleeve | 120/10 |
| 7 | C7 | Cand. | S3902 | 7C7 | Clear | 130V | 2500 | 35 | C-7A | 1 7/8" | Sleeve | 120/10 |
| 10 | C7 | Cand. | S3903 | 10C7 | Clear | 130V | 2500 | 60 | C-7A | 2 1/8" | Sleeve | 120/10 |
| 10 | C7 | DC Bayonet | S3904 | 10C7/DC | Clear | 130V | 2500 | 60 | C-7A | 2 1/8" | Sleeve | 120/10 |
| 15 | T6 | Cand. | S3910 | 15T6 | Clear | 130V | 2500 | 95 | C-5A | 3 1/16" | Sleeve | 120/10 |
| 15 | T6 | Cand. | S3912 | 15T6 | Clear | 145V | 2500 | 95 | C-5A | 3 1/16" | Sleeve | 120/10 |
| 15 | T6 | Cand. | S3315 | 15T6/F | Frost | 120V | 2500 | 95 | C-5A | 4" | Sleeve | 500/25 |

general service lamps



NEW PRODUCT INFORMATION

Vintage style incandescent lamps

Historically accurate.
Beautifully reproduced.

Satco's Vintage Lamps are truthful, historic reproductions from this important and ever-popular era in lighting and architecture. No detail is overlooked, making these high-quality lamps the perfect solution when achieving authenticity and atmosphere are the goals.

Features


- Classic, warm glow from clearly visible filaments
- Historic restoration quality
- Perfect for hotel, theater, restaurants and other themed venues
- Authentic reproductions display beautifully
- Attractive full color packaging



S2411, S2412,
S2419



S2413,
S2423



S2414



S2415



S2416



S2417



S2418



S2420




S2421,
S2422

NEW

Available
February 2014



S2424



S2425



NEW PRODUCT INFORMATION

| Item Number | Lamp Description | Wattage | Coil Design | Volts | Base | Finish | Hours | Lumens | Master/Inner |
|-------------|----------------------------|---------|-------------|-------|------|--------|-------|--------|--------------|
| S2411 | 25A19/CL/120V VINTAGE | 25 | Quad Loop | 120V | E26 | Clear | 3000 | 50 | 48/6 |
| S2412 | 40A19/CL/120V VINTAGE | 40 | Quad Loop | 120V | E26 | Clear | 3000 | 130 | 48/6 |
| S2419 | 60A19/CL/120V VINTAGE | 60 | Quad Loop | 120V | E26 | Clear | 3000 | 240 | 48/6 |
| S2413 | 40ST19/CL/15S/120V VINTAGE | 40 | Cage Style | 120V | E26 | Clear | 3000 | 135 | 48/6 |
| S2414 | 40ST19/CL/9S/120V VINTAGE | 40 | Hairpin | 120V | E26 | Clear | 3000 | 165 | 48/6 |
| S2415 | 20T9/CL/120V VINTAGE | 20 | Hairpin | 120V | E26 | Clear | 3000 | 20 | 48/6 |
| S2416 | 40T14/CL/32S/120V VINTAGE | 40 | Spiral | 120V | E26 | Clear | 3000 | 135 | 50/10 |
| S2417 | 40T14/CL/15S/120V VINTAGE | 40 | Cage Style | 120V | E26 | Clear | 3000 | 135 | 50/10 |
| S2418 | 25CFC/7S/120V VINTAGE | 25 | Deco Carbon | 120V | E12 | Clear | 3000 | 45 | 50/10 |
| S2420 | 40T9/GOLD/9S/120V VINTAGE | 40 | Cage Style | 120V | E12 | Gold | 3000 | 20 | 50/10 |
| S2421 | 40T9/CL/12S/120V VINTAGE | 40 | Hairpin | 120V | E26 | Clear | 3000 | 160 | 50/10 |
| S2422 | 60T9/CL/12S/120V VINTAGE | 60 | Hairpin | 120V | E26 | Clear | 3000 | 230 | 50/10 |
| S2423 | 60ST19/CL/15S/120V VINTAGE | 60 | Cage Style | 120V | E26 | Clear | 3000 | 240 | 48/6 |
| S2424 | 40A15/CL/13S/120V VINTAGE | 40 | Cage Style | 120V | E26 | Clear | 2000 | 160 | 50/10 |
| S2425 | 40G25/CL/15S/120V VINTAGE | 40 | Cage Style | 120V | E26 | Clear | 3000 | 160 | 48/6 |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



NEW PRODUCT INFORMATION

Vintage Style LED filament lamps

Features

- LED with a traditional vintage look and feel
- Amber finish
- Omni-directional light source
- Smooth dimming
- 2200 & 2300K - warm tone color temperature
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp location
- Approved for totally enclosed fixtures
- cUL listed



S9577,
S9578, S9579
ST19

S9584
G25

S9583
A19

S9585
ST19

S9586
C35

S9587
CA35

S9588
T9

LED Filament Lamps



| Item Number | Lamp Description | W | Bulb Type | Base | V | Finish | CCT | Lm | CRI | M.O.L. (Inches) | Life/ Hrs. | UPC |
|-------------|------------------------------|-----|-----------|------|-----|--------|-------|-----|-----|-----------------|------------|--------------|
| S9577 | 2.5ST19/AMB/LED/E26/23K/120V | 2.5 | ST19 | E26 | 120 | Amber | 2300K | 220 | 80 | 5 3/8 | 15K | 045923095771 |
| S9578 | 4.5ST19/AMB/LED/E26/23K/120V | 4.5 | ST19 | E26 | 120 | Amber | 2300K | 400 | 80 | 5 3/8 | 15K | 045923095788 |
| S9579 | 6.5ST19/AMB/LED/E26/23K/120V | 6.5 | ST19 | E26 | 120 | Amber | 2300K | 650 | 80 | 5 3/8 | 15K | 045923095795 |
| S9583 | 4.5A19/AMB/LED/E26/22K/120V | 4.5 | A19 | E26 | 120 | Amber | 2200K | 380 | 80 | 4 1/8 | 15K | 045923095832 |
| S9584 | 4.5G25/AMB/LED/E26/22K/120V | 4.5 | G25 | E26 | 120 | Amber | 2200K | 380 | 80 | 4 3/8 | 15K | 045923095849 |
| S9585 | 4.5ST19/AMB/LED/E26/22K/120V | 4.5 | ST19 | E26 | 120 | Amber | 2200K | 380 | 80 | 5 1/2 | 15K | 045923095856 |
| S9586 | 4CTA/LED/AMB/22K/120V | 4 | C35 | E12 | 120 | Amber | 2200K | 300 | 80 | 4 5/16 | 15K | 045923095863 |
| S9587 | 4CFA/LED/AMB/22K/120V | 4 | CA35 | E12 | 120 | Amber | 2200K | 300 | 80 | 5 | 15K | 045923095870 |
| S9588 | 6.5T9/AMB/LED/E26/22K/120V | 6.5 | T9 | E26 | 120 | Amber | 2200K | 620 | 80 | 12 | 15K | 045923095887 |

Pack: Master 24 / Inner 6/1

LED SPECIALTY LAMPS

LED filament lamps

Applications / Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp location
- Approved for totally enclosed fixtures
- cUL listed



LED Filament Lamps




| Item Number | Lamp Description | W | Bulb Type | Base | V | Finish | CCT | Lm | CRI | M.O.L. (Inches) | Life/ Hrs. | UPC | Pack |
|-------------|-----------------------------|-----|-----------|------|-----|--------|-------|-----|-----|-----------------|------------|--------------|------|
| S9560 | 4.5A15/CL/LED/E26/27K/120V | 4.5 | A15 | E26 | 120 | Clear | 2700K | 450 | 80 | 3 3/8 | 15K | 045923095603 | 24/6 |
| S9561 | 4.5A19/CL/LED/E26/27K/120V | 4.5 | A19 | E26 | 120 | Clear | 2700K | 450 | 80 | 4 1/8 | 15K | 045923095610 | 24/6 |
| S9562 | 6.5A19/CL/LED/E26/27K/120V | 6.5 | A19 | E26 | 120 | Clear | 2700K | 810 | 80 | 4 1/8 | 15K | 045923095627 | 24/6 |
| S9563* | 4.5G25/CL/LED/E26/27K/120V | 4.5 | G25 | E26 | 120 | Clear | 2700K | 450 | 80 | 4 3/8 | 25K | 045923095634 | 24/6 |
| S9564 | 6.5G25/CL/LED/E26/27K/120V | 6.5 | G25 | E26 | 120 | Clear | 2700K | 810 | 80 | 4 3/8 | 15K | 045923095641 | 24/6 |
| S9565 | 4.5G40/CL/LED/E26/27K/120V | 4.5 | G40 | E26 | 120 | Clear | 2700K | 450 | 80 | 6 1/2 | 15K | 045923095658 | 24/6 |
| S9566 | 6.5G40/CL/LED/E26/27K/120V | 6.5 | G40 | E26 | 120 | Clear | 2700K | 810 | 80 | 6 1/2 | 15K | 045923095665 | 24/6 |
| S9820+ | 2W CTC/LED/27K/CL/120V/AG | 2 | C35 | E12 | 120 | Clear | 2700K | 190 | 80 | 3 7/8 | 15K | 045923098208 | 24/6 |
| S9821+ | 2W CFC/LED/27K/CL/120V/AG | 2 | CA35 | E12 | 120 | Clear | 2700K | 190 | 80 | 4 11/16 | 15K | 045923098215 | 24/6 |
| S9822+ | 4W CTC/LED/27K/CL/120V/AG | 4 | C35 | E12 | 120 | Clear | 2700K | 340 | 80 | 3 7/8 | 15K | 045923098222 | 24/6 |
| S9823+ | 4W CFC/LED/27K/CL/120V/AG | 4 | CA35 | E12 | 120 | Clear | 2700K | 340 | 80 | 4 11/16 | 15K | 045923098239 | 24/6 |
| S9567* | 2.5W ETC/LED/27K/120V | 2.5 | C35 | E26 | 120 | Clear | 2700K | 250 | 80 | 3 1/2 | 15K | 045923095672 | 24/6 |
| S9568* | 2.5W CTC/LED/27K/120V | 2.5 | C35 | E12 | 120 | Clear | 2700K | 250 | 80 | 4 5/16 | 15K | 045923095689 | 24/6 |
| S9569* | 4.5W ETC/LED/27K/120V | 4.5 | C35 | E26 | 120 | Clear | 2700K | 450 | 80 | 3 1/2 | 15K | 045923095696 | 24/6 |
| S9570* | 4.5W CTC/LED/27K/120V | 4.5 | C35 | E12 | 120 | Clear | 2700K | 450 | 80 | 4 5/16 | 15K | 045923095702 | 24/6 |
| S9571 | 2.5W EFC/LED/27K/120V | 2.5 | CA35 | E26 | 120 | Clear | 2700K | 250 | 80 | 4 5/16 | 15K | 045923095719 | 24/6 |
| S9572 | 2.5W CFC/LED/27K/120V | 2.5 | CA35 | E12 | 120 | Clear | 2700K | 250 | 80 | 5 | 15K | 045923095726 | 24/6 |
| S9573 | 4.5W EFC/LED/27K/120V | 4.5 | CA35 | E26 | 120 | Clear | 2700K | 450 | 80 | 4 5/16 | 15K | 045923095733 | 24/6 |
| S9574 | 4.5W CFC/LED/27K/120V | 4.5 | CA35 | E12 | 120 | Clear | 2700K | 450 | 80 | 5 | 15K | 045923095740 | 24/6 |
| S9575 | 4.5BT15/CL/LED/E26/27K/120V | 4.5 | BT15 | E26 | 120 | Clear | 2700K | 450 | 80 | 4 1/8 | 15K | 045923095757 | 24/6 |
| S9576 | 6.5BT15/CL/LED/E26/27K/120V | 6.5 | BT15 | E26 | 120 | Clear | 2700K | 810 | 80 | 4 1/8 | 15K | 045923095764 | 24/6 |
| S9581 | 6.5ST19/CL/LED/E26/27K/120V | 6.5 | ST19 | E26 | 120 | Clear | 2700K | 810 | 80 | 5 1/2 | 15K | 045923095818 | 24/6 |
| S9582 | 6.5T9/CL/LED/E26/27K/120V | 6.5 | T9 | E26 | 120 | Clear | 2700K | 800 | 80 | 12 | 15K | 045923095825 | 24/6 |
| S9580 | 4.5T10/LED/E26/27K/120V | 4.5 | T10 | E26 | 120 | Clear | 2700K | 430 | 80 | 5 | 15K | 045923095801 | 24/6 |

*AG - All glass envelope



VINTAGE STYLE Incandescent

Historically Accurate Bulbs all beautifully reproduced



- Classic warm glow from clearly visible filaments
- Historic restoration quality
- Perfect for hotel, theater, restaurants & other themed venues
- Authentic reproductions display beautifully.
- Attractive full - color packaging

| ITEM NUMBER | DESCRIPTION | WATTAGE | COIL DESIGN | VOLTS | BASE | FINISH | HOURS | LUMENS | CARTON | EACH | MASTER |
|-------------|----------------------------|---------|-------------|-------|------|--------|-------|--------|--------|--------|--------|
| S2411 | 25A19/CL/120V VINTAGE | 25 | Quad Loop | 120V | E26 | Clear | 3000 | 50 | 48/6 | \$5.55 | \$4.85 |
| S2412 | 40A19/CL/120V VINTAGE | 40 | Quad Loop | 120V | E26 | Clear | 3000 | 130 | 48/6 | \$5.55 | \$4.85 |
| S2413 | 40ST19/CL/15S/120V VINTAGE | 40 | Cage Style | 120V | E26 | Clear | 3000 | 135 | 48/6 | \$5.65 | \$4.95 |
| S2414 | 40ST19/CL/9S/120V VINTAGE | 40 | Hairpin | 120V | E26 | Clear | 3000 | 165 | 48/6 | \$5.65 | \$4.95 |
| S2415 | 20T9/CL/120V VINTAGE | 20 | Hairpin | 120V | E26 | Clear | 3000 | 20 | 48/6 | \$5.45 | \$4.75 |
| S2416 | 40T14/CL/32S/120V VINTAGE | 40 | Spiral | 120V | E26 | Clear | 3000 | 135 | 50/10 | \$5.65 | \$4.95 |
| S2417 | 40T14/CL/15S/120V VINTAGE | 40 | Cage Style | 120V | E26 | Clear | 3000 | 135 | 50/10 | \$5.65 | \$4.95 |
| S2418 | 25CFC/7S/120V VINTAGE | 25 | Deco Carbon | 120V | E12 | Clear | 3000 | 45 | 50/10 | \$3.95 | \$3.25 |



National Toll-Free: 1-800-43-SATCO (1-800-437-2826)

Visit Our Web Site at: www.satco.com

Also see us on



EXECUTIVE OFFICES & WAREHOUSE; NEW YORK, 110 Heartland Blvd., Brentwood, NY 11717 • 800-437-2826 • (631) 243-2022 • FAX (631) 243-2027
 FLORIDA, 900 N.W. 159th Drive, Miami, FL 33169 • 800-437-2826 • (305) 624-2044 • FAX (305) 623-0286
 TEXAS, 2000 Valwood Parkway, Farmers branch, TX 75234 • 800-437-2826 • (972) 247-2437 • FAX (972) 247-5408
 CALIFORNIA, 31288 San Benito St., Hayward, CA 94544 • 800-437-2826 • (510) 487-4822 • FAX (510) 487-8955
 WASHINGTON, 4710 116th St. S.W., Mukilteo, WA 98275 • 800-437-2826 • (425) 789-3300 • FAX (425) 789-3310
 PUERTO RICO, Bldg 3, Campeche St. 23 Julio N. Matos Industrial Park • Bo Martin Gonzales Carolina, PR 00984 • (787) 757-3510 • FAX (787) 757-3540

Not responsible for typographical errors.

Fan *Bulbs*

130 Volt / 2500 Hours



Frosted

Medium Base
S3815 25 Watt
S3811 40 Watt
S3871 60 Watt

Packing: Individually Boxed
 500 Master, 25/Inner



Clear

Medium Base
S3814 25Watt
S3810 40 Watt
S3870 60 Watt

Packing: Individually Boxed
 500 Master, 25/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | A15 | Med. | S3814 | 25A15 | Clear | 130V | 2500 | 130 | C-9 | 3 1/2" | Box | 500/25 |
| 25 | A15 | Med. | S3815 | 25A15/F | Frosted | 130V | 2500 | 120 | C-9 | 3 1/2" | Box | 500/25 |
| 40 | A15 | Med. | S3810 | 40A15 | Clear | 130V | 2500 | 290 | C-9 | 3 1/2" | Box | 500/25 |
| 40 | A15 | Med. | S3811 | 40A15/F | Frosted | 130V | 2500 | 280 | C-9 | 3 1/2" | Box | 500/25 |
| 60 | A15 | Med. | S3870 | 60A15 | Clear | 130V | 2500 | 580 | C-9 | 3 1/2" | Box | 500/25 |
| 60 | A15 | Med. | S3871 | 60A15/F | Frosted | 130V | 2500 | 530 | C-9 | 3 1/2" | Box | 500/25 |

general service lamps

2500 Hours / 130 Volts

Medium Base



Clear

Medium Base
S3948 15 Watt
Packing: Boxed, 2 Pack
120 Master, 60 2-Packs
Sold Per Lamp



Frosted

Medium Base
S3949 15 Watt
Packing: Boxed, 2 Pack
120 Master, 60 2-Packs
Sold Per Lamp



Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------|
| 15 | A15 | Med. | S3948 | 15A15 | Clear | 130V | 2500 | 100 | C-9 | 3 1/2" | Box/2 | 120 |
| 15 | A15 | Med. | S3949 | 15A15/F | Frosted | 130V | 2500 | 100 | C-9 | 3 1/2" | Box/2 | 120 |

general service lamps

A19 Household Brass Base



Lamps 2 Pack

120 Volt / 1500 Hours

Medium Base



Clear



Frosted



Not Shown
Actual Size

Medium Base

- S6040** 25 Watt
- S6041** 40 Watt
- S6042** 60 Watt
- S6043** 75 Watt
- S6044** 100 Watt

Packing: Boxed, 2 Pack
120 Master, 60 2-Packs
Sold Per Lamp

Medium Base

- S6050** 25 Watt
- S6051** 40 Watt
- S6052** 60 Watt
- S6053** 75 Watt
- S6054** 100 Watt

Packing: Boxed, 2 Pack
120 Master, 60 2-Packs
Sold Per Lamp

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack Type | Mst.Ctn. |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|-----------|----------|
| 25 | A19 | Med. | S6040 | 25A19 | Clear | 120V | 1500 | 185 | C-9 | 4 1/8" | Box/2 | 120 |
| 25 | A19 | Med. | S6050 | 25A19/F | Frosted | 120V | 1500 | 185 | C-9 | 4 1/8" | Box/2 | 120 |
| 40 | A19 | Med. | S6041 | 40A19 | Clear | 120V | 1500 | 340 | C-9 | 4 1/8" | Box/2 | 120 |
| 40 | A19 | Med. | S6051 | 40A19/F | Frosted | 120V | 1500 | 340 | C-9 | 4 1/8" | Box/2 | 120 |
| 60 | A19 | Med. | S6042 | 60A19 | Clear | 120V | 1500 | 610 | C-9 | 4 1/8" | Box/2 | 120 |
| 60 | A19 | Med. | S6052 | 60A19/F | Frosted | 120V | 1500 | 610 | C-9 | 4 1/8" | Box/2 | 120 |
| 75 | A19 | Med. | S6043 | 75A19 | Clear | 120V | 1500 | 800 | C-9 | 4 1/8" | Box/2 | 120 |
| 75 | A19 | Med. | S6053 | 75A19/F | Frosted | 120V | 1500 | 800 | C-9 | 4 1/8" | Box/2 | 120 |
| 100 | A19 | Med. | S6044 | 100A19 | Clear | 120V | 1500 | 1150 | C-9 | 4 1/8" | Box/2 | 120 |
| 100 | A19 | Med. | S6054 | 100A19/F | Frosted | 120V | 1500 | 1150 | C-9 | 4 1/8" | Box/2 | 120 |

general service lamps

A19 Household Lamps 2 Pack

2500 Hours / 130 Volt

Medium Base

Not Shown
Actual Size



Frosted



Clear



Medium Base

- S3950** 25 Watt
- S3951** 40 Watt
- S3952** 60 Watt
- S3953** 75 Watt
- S3954** 100 Watt

Packing: Boxed, 2 Pack
120 Master, 60 2-Packs
Sold Per Lamp

Medium Base

- S3940** 25 Watt
- S3941** 40 Watt
- S3942** 60 Watt
- S3943** 75 Watt
- S3944** 100 Watt

Packing: Boxed, 2 Pack
120 Master, 60 2-Packs
Sold Per Lamp

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack Type | Mst.Ctn. |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|-----------|----------|
| 25 | A19 | Med. | S3940 | 25A19 | Clear | 130V | 2500 | 185 | CC-6 | 4 1/8" | Box/2 | 120 |
| 25 | A19 | Med. | S3950 | 25A19/F | Frosted | 130V | 2500 | 185 | CC-6 | 4 1/8" | Box/2 | 120 |
| 40 | A19 | Med. | S3941 | 40A19 | Clear | 130V | 2500 | 320 | C-9 | 4 1/8" | Box/2 | 120 |
| 40 | A19 | Med. | S3951 | 40A19/F | Frosted | 130V | 2500 | 320 | C-9 | 4 1/8" | Box/2 | 120 |
| 60 | A19 | Med. | S3942 | 60A19 | Clear | 130V | 2500 | 580 | C-9 | 4 1/8" | Box/2 | 120 |
| 60 | A19 | Med. | S3952 | 60A19/F | Frosted | 130V | 2500 | 580 | C-9 | 4 1/8" | Box/2 | 120 |
| 75 | A19 | Med. | S3943 | 75A19 | Clear | 130V | 2500 | 760 | C-9 | 4 1/8" | Box/2 | 120 |
| 75 | A19 | Med. | S3953 | 75A19/F | Frosted | 130V | 2500 | 760 | C-9 | 4 1/8" | Box/2 | 120 |
| 100 | A19 | Med. | S3944 | 100A19 | Clear | 130V | 2500 | 1100 | C-9 | 4 1/8" | Box/2 | 120 |
| 100 | A19 | Med. | S3954 | 100A19/F | Frosted | 130V | 2500 | 1100 | C-9 | 4 1/8" | Box/2 | 120 |

130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE

| | | | | | | | | | | | | |
|----|-----|------|--------------|----------|---------|------|------|-----|------|--------|-------|-----|
| 23 | A19 | Med. | S3940 | 25A19 | Clear | 130V | 5000 | 140 | CC-6 | 4 1/8" | Box/2 | 120 |
| 23 | A19 | Med. | S3950 | 25A19/F | Frosted | 130V | 5000 | 140 | CC-6 | 4 1/8" | Box/2 | 120 |
| 36 | A19 | Med. | S3941 | 40A19 | Clear | 130V | 5000 | 235 | C-9 | 4 1/8" | Box/2 | 120 |
| 36 | A19 | Med. | S3951 | 40A19/F | Frosted | 130V | 5000 | 235 | C-9 | 4 1/8" | Box/2 | 120 |
| 53 | A19 | Med. | S3942 | 60A19 | Clear | 130V | 5000 | 445 | C-9 | 4 1/8" | Box/2 | 120 |
| 53 | A19 | Med. | S3952 | 60A19/F | Frosted | 130V | 5000 | 445 | C-9 | 4 1/8" | Box/2 | 120 |
| 66 | A19 | Med. | S3943 | 75A19 | Clear | 130V | 5000 | 570 | C-9 | 4 1/8" | Box/2 | 120 |
| 66 | A19 | Med. | S3953 | 75A19/F | Frosted | 130V | 5000 | 570 | C-9 | 4 1/8" | Box/2 | 120 |
| 90 | A19 | Med. | S3944 | 100A19 | Clear | 130V | 5000 | 810 | C-9 | 4 1/8" | Box/2 | 120 |
| 90 | A19 | Med. | S3954 | 100A19/F | Frosted | 130V | 5000 | 810 | C-9 | 4 1/8" | Box/2 | 120 |

general service lamps

A19 Household Brass Base



Lamps 4 Pack

120 Volt / 1500 Hours

Medium Base



Not Shown
Actual Size

Soft White

Medium Base

S1810 40 Watt

S1811 60 Watt

S1812 75 Watt

S1813 100 Watt

Packing: Boxed, Pack

48 Master, 12 4-Packs

Sold Per Lamp



Frosted

Medium Base

S1711 40 Watt

S1712 60 Watt

S1713 75 Watt

S1714 100 Watt

Packing: Boxed, 4 Pack

48 Master, 12 4-Packs

Sold Per Lamp



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------|
| 40 | A19 | Med. | S1711 | 40A19/F | Frosted | 120V | 1500 | 340 | C-9 | 4 1/8" | Box/4 | 48 |
| 40 | A19 | Med. | S1810 | 40A19/W | White | 120V | 1500 | 280 | C-9 | 4 1/8" | Box/4 | 48 |
| 60 | A19 | Med. | S1712 | 60A19/F | Frosted | 120V | 1500 | 610 | C-9 | 4 1/8" | Box/4 | 48 |
| 60 | A19 | Med. | S1811 | 60A19/W | White | 120V | 1500 | 500 | C-9 | 4 1/8" | Box/4 | 48 |
| 75 | A19 | Med. | S1713 | 75A19/F | Frosted | 120V | 1500 | 800 | C-9 | 4 1/8" | Box/4 | 48 |
| 75 | A19 | Med. | S1812 | 75A19/W | White | 120V | 1500 | 650 | C-9 | 4 1/8" | Box/4 | 48 |
| 100 | A19 | Med. | S1714 | 100A19/F | Frosted | 120V | 1500 | 1150 | C-9 | 4 1/8" | Box/4 | 48 |
| 100 | A19 | Med. | S1813 | 100A19/W | White | 120V | 1500 | 950 | C-9 | 4 1/8" | Box/4 | 48 |

general service lamps

Not Shown Actual Size

Medium Base **Lamps**



**Long Life
Commercial Service**

Frosted **S3934** 75 Watt A21
 Medium Base **S3935** 100 Watt A21
 S3936 100 Watt A23

Packing: Individually Sleeved
 120 Master, 6/Inner

Long Neck A Lamps

- 130 Volt Frosted
- 12,500 Hrs. Avg. Life (when burned at 120v).
- Resists Power Surges.



**Left Hand
Thread A19**

Frosted **S6010** 100 Watt
 Medium Base

Packing: Individually Sleeved
 120 Master, 6/Inner

- Left-hand thread to prevent theft.
- Uses: construction, work sites, hotels, restaurants, etc.

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|----------------|---------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 100 | A19 | Med. | S6010 | 100A19/LHT/F | Frosted | 120V | 2000 | 1200 | C-9 | 4 1/8" | Sleeve | 120/6 |
| 75 | A21 | Med. | S3934 | 75A21/IF/130V | Frosted | 130V | 5000 | 680 | C-9 | 5 5/16" | Sleeve | 120/6 |
| 100 | A21 | Med. | S3935 | 100A21/IF/130V | Frosted | 130V | 5000 | 1030 | C-9 | 5 5/16" | Sleeve | 120/6 |
| 100 | A23 | Med. | S3936 | 100A23/IF/130V | Frosted | 130V | 5000 | 1030 | C-9 | 6 1/16" | Sleeve | 120/6 |

130 Volt Bulb Specifications Operated On a 120 Volt Line

| | | | | | | | | | | | | |
|----|-----|------|--------------|----------------|---------|------|--------|-----|-----|---------|--------|-------|
| 66 | A21 | Med. | S3934 | 75A21/IF/130V | Frosted | 130V | 12,500 | 515 | C-9 | 5 5/16" | Sleeve | 120/6 |
| 88 | A21 | Med. | S3935 | 100A21/IF/130V | Frosted | 130V | 12,500 | 780 | C-9 | 5 5/16" | Sleeve | 120/6 |
| 88 | A23 | Med. | S3936 | 100A23/IF/130V | Frosted | 130V | 12,500 | 780 | C-9 | 6 1/16" | Sleeve | 120/6 |

A19 Specialty Brass Base



Lamps

Medium Base

Not Shown Actual Size



Incandescent Black Light

Medium Base
120 Volt /480 Hrs. Avg. Life
S3920 75 Watt
Packing: Individually Boxed
96 Master, 6/Inner

Bug Light

Medium Base
130 Volt /2000 Hrs. Avg. Life
S3859 40 Watt Yellow
S3938 60 Watt Yellow
S3939 100 Watt Yellow
Packing: Boxed, 2 Pack
24 Master, 12 2-Packs
Sold Per Lamp

Silver Crown

Medium Base
130 Volt /1500 Hrs. Avg. Life
S3955 60A19/SL
S3956 100A19/SL
Packing: Individually Boxed
24 Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|-------------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 40 | A19 | Med. | S3859 | 40A/Y | Bug | 130V | 2000 | - | C-9 | 4 1/8" | Box/2 | 24 |
| 60 | A19 | Med. | S3938 | 60A/Y | Bug | 130V | 2000 | - | C-9 | 4 1/8" | Box/2 | 24 |
| 100 | A19 | Med. | S3939 | 100A/Y | Bug | 130V | 2000 | - | C-9 | 4 1/8" | Box/2 | 24 |
| 75 | A19 | Med. | S3920 | 75A/BL | Black Light | 120V | 480 | - | C-9 | 4 1/8" | Box | 96/6 |
| 60 | A19 | Med. | S3955 | 60A/SL | Silver | 130V | 1500 | 580 | C-9 | 4 1/8" | Box | 24 |
| 100 | A19 | Med. | S3956 | 100A/SL | Silver | 130V | 1500 | 960 | C-9 | 4 1/8" | Box | 24 |

general service lamps

1000 Hours

A19 Transparent

Medium Base



25W
Medium Base 130 Volt

S6080 Transparent Red
S6081 Transparent Green
S6082 Transparent Blue
S6083 Transparent Yellow
 Packing: Individually Sleeved
 24/Master, 12 Inner

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | A19 | Med. | S6080 | 25A/TR | Red | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 25 | A19 | Med. | S6081 | 25A/TG | Green | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 25 | A19 | Med. | S6082 | 25A/TB | Blue | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 25 | A19 | Med. | S6083 | 25A/TY | Yellow | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |

general service lamps

Party *Bulbs* Brass Base



A19 Ceramic

1000 Hours

Medium Base

Not Shown Actual Size



25W
Medium Base
130 Volt

- S6090** Ceramic Red
- S6091** Ceramic Green
- S6092** Ceramic Blue
- S6093** Ceramic Yellow

Packing: Individually Sleeved
24/Master, 12 Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | A19 | Med. | S6090 | 25A/R | Red | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 25 | A19 | Med. | S6091 | 25A/G | Green | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 25 | A19 | Med. | S6092 | 25A/B | Blue | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 25 | A19 | Med. | S6093 | 25A/Y | Yellow | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |

specialty lamps

1000 Hours

Medium Base

Not Shown Actual Size



40W
Medium Base
130 Volt

S4980 Ceramic Red
S4981 Ceramic Blue
S4982 Ceramic Green
S4983 Ceramic Yellow
Packing: Individually Boxed
24/Master, 12/Inner

60W
Medium Base
130 Volt

S4984 Ceramic Red
S4985 Ceramic Blue
S4986 Ceramic Green
S4987 Ceramic Yellow
Packing: Individually Boxed
24/Master, 12/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|-------------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 40 | A19 | Med. | S4980 | 40A/R | Cer. Red | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 40 | A19 | Med. | S4981 | 40A/B | Cer. Blue | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 40 | A19 | Med. | S4982 | 40A/G | Cer. Green | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 40 | A19 | Med. | S4983 | 40A/Y | Cer. Yellow | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 60 | A19 | Med. | S4984 | 60A/R | Cer. Red | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 60 | A19 | Med. | S4985 | 60A/B | Cer. Blue | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 60 | A19 | Med. | S4986 | 60A/G | Cer. Green | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |
| 60 | A19 | Med. | S4987 | 60A/Y | Cer. Yellow | 130V | 1000 | n/a | C-9 | 4 1/8" | Sleeve | 24/12 |

specialty lamps

A19 Household Lamps 3 Pack



130 Volt



Sold Per Pack
Full Cases Only

Not Shown Actual Size

Soft White

Medium Base

- S3991** 40 Watt
- S3992** 60 Watt
- S3993** 75 Watt
- S3994** 100 Watt

Packing: Boxed, 3 Pack
120 Master, 40 3-Packs

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------|
| 40 | A19 | Med. | S3991 | 40A19/W | White | 130V | 1250 | 288 | C-9 | 4 1/8" | Box/3 | 40 |
| 60 | A19 | Med. | S3992 | 60A19/W | White | 130V | 1250 | 576 | C-9 | 4 1/8" | Box/3 | 40 |
| 75 | A19 | Med. | S3993 | 75A19/W | White | 130V | 1250 | 747 | C-9 | 4 1/8" | Box/3 | 40 |
| 100 | A19 | Med. | S3994 | 100A19/W | White | 130V | 1250 | 1107 | C-9 | 4 1/8" | Box/3 | 40 |

general service lamps



A19 Household Lamps 4 Pack

130 Volt



Clear

Soft White

Sold Per Pack
Full Cases Only

- Medium Base
S4020 40 Watt
S4021 60 Watt
S4022 75 Watt
S4023 100 Watt

Packing: Boxed, 4 Pack
120 Master, 30 4-Packs

- Medium Base
S4010 40 Watt
S4011 60 Watt
S4012 75 Watt
S4013 100 Watt

Packing: Boxed, 4 Pack
120 Master, 30 4-Packs

Not Shown
Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn. |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|----------|
| 40 | A19 | Med. | S4020 | 40A19 | Clear | 130V | 1000 | 320 | C-9 | 4 1/8" | Box/4 | 30 |
| 40 | A19 | Med. | S4010 | 40A19/W | White | 130V | 1000 | 288 | C-9 | 4 1/8" | Box/4 | 30 |
| 60 | A19 | Med. | S4021 | 60A19 | Clear | 130V | 1000 | 640 | C-9 | 4 1/8" | Box/4 | 30 |
| 60 | A19 | Med. | S4011 | 60A19/W | White | 130V | 1000 | 576 | C-9 | 4 1/8" | Box/4 | 30 |
| 75 | A19 | Med. | S4022 | 75A19 | Clear | 130V | 1000 | 830 | C-9 | 4 1/8" | Box/4 | 30 |
| 75 | A19 | Med. | S4012 | 75A19/W | White | 130V | 1000 | 747 | C-9 | 4 1/8" | Box/4 | 30 |
| 100 | A19 | Med. | S4023 | 100A19 | Clear | 130V | 1000 | 1230 | C-9 | 4 1/8" | Box/4 | 30 |
| 100 | A19 | Med. | S4013 | 100A19/W | White | 130V | 1000 | 1107 | C-9 | 4 1/8" | Box/4 | 30 |

130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE

| | | | | | | | | | | | | |
|----|-----|------|--------------|----------|-------|------|------|-----|-----|--------|-------|----|
| 36 | A19 | Med. | S4020 | 40A19 | Clear | 130V | 3000 | 230 | C-9 | 4 1/8" | Box/4 | 30 |
| 36 | A19 | Med. | S4010 | 40A19/W | White | 130V | 3000 | 207 | C-9 | 4 1/8" | Box/4 | 30 |
| 53 | A19 | Med. | S4021 | 60A19 | Clear | 130V | 3000 | 460 | C-9 | 4 1/8" | Box/4 | 30 |
| 53 | A19 | Med. | S4011 | 60A19/W | White | 130V | 3000 | 414 | C-9 | 4 1/8" | Box/4 | 30 |
| 66 | A19 | Med. | S4022 | 75A19 | Clear | 130V | 3000 | 598 | C-9 | 4 1/8" | Box/4 | 30 |
| 66 | A19 | Med. | S4012 | 75A19/W | White | 130V | 3000 | 538 | C-9 | 4 1/8" | Box/4 | 30 |
| 90 | A19 | Med. | S4023 | 100A19 | Clear | 130V | 3000 | 885 | C-9 | 4 1/8" | Box/4 | 30 |
| 90 | A19 | Med. | S4013 | 100A19/W | White | 130V | 3000 | 797 | C-9 | 4 1/8" | Box/4 | 30 |

general service lamps



A19 Safety Coated



Shatterproof *Lamps* Brass Base 130 Volt

Medium Base



- Rubber coating contains glass particles should bulb break.
- Heavy duty shatter proof bulb.
- Long life.
- Resists power surges – 130V.
- Five support filament to withstand vibration and impact.
- Uses: Workshops, garages, construction areas, bathrooms, or any hazardous environments



Frosted

Medium Base

S3927 60 Watt

S3928 75 Watt

S3929 100 Watt

Packing: Boxed, 2 Pack
12 Master, 12 2-Packs
Sold Per Pack

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|---|-----------|------|-----------------|--------------|---------|-------|------------------|--------|----------|--------|------------|-----------|
| 60 | A19 | Med. | S3927 | 60A19/RS/TF | Frosted | 130V | 5000 | 520 | C-9 | 4 1/8" | 2/Pks | 12 |
| 75 | A19 | Med. | S3928 | 75A19/RS/TF | Frosted | 130V | 5000 | 680 | C-9 | 4 1/8" | 2/Pks | 12 |
| 100 | A19 | Med. | S3929 | 100A19/RS/TF | Frosted | 130V | 5000 | 960 | C-9 | 4 1/8" | 2/Pks | 12 |
| 130 Volt Bulb Specifications Operated On a 120 Volt Line | | | | | | | | | | | | |
| 53 | A19 | Med. | S3927 | 60A19/RS/TF | Frosted | 130V | 12,500 | 395 | C-9 | 4 1/8" | 2/Pks | 12 |
| 66 | A19 | Med. | S3928 | 75A19/RS/TF | Frosted | 130V | 12,500 | 515 | C-9 | 4 1/8" | 2/Pks | 12 |
| 88 | A19 | Med. | S3929 | 100A19/RS/TF | Frosted | 130V | 12,500 | 730 | C-9 | 4 1/8" | 2/Pks | 12 |

general service lamps



Safety Coated

Medium Base
A21 130 Volt
S3972 75 Watt
S3973 100 Watt
Packing: Boxed, 2 Pack,
24 Master, 12 2-Packs
Sold Per Pack



Rough Service

Medium Base
A19 130 Volt
S3969 50 Watt
S3970 75 Watt
S3971 100 watt
Packing: Boxed, 2 Pack,
24 Master, 12 2-Packs
Sold Per Pack

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|---------|------------|-----------|
| 50 | A19 | Med. | S3969 | 50A/RS | Frost | 130V | 2500 | 320 | C-9 | 4 1/8" | Box/2 | 24 |
| 75 | A19 | Med. | S3970 | 75A/RS | Frost | 130V | 2500 | 620 | C-9 | 4 1/8" | Box/2 | 24 |
| 100 | A19 | Med. | S3971 | 100A/RS | Frost | 130V | 2500 | 880 | C-9 | 4 1/8" | Box/2 | 24 |
| 75 | A21 | Med. | S3972 | 75A21/TF | Frost | 130V | 2500 | 620 | C-9 | 5 5/16" | Box/2 | 24 |
| 100 | A21 | Med. | S3973 | 100A21/TF | Frost | 130V | 2500 | 880 | C-9 | 5 5/16" | Box/2 | 24 |

general service lamps



3-Way



Household Lamps

Not Shown Actual Size



3 Way/Med.

Soft White
 Medium Base
 120 Volt
S1820 30/70/100 Watt
S1821 50/100/150 Watt
S1823 50/200/250 Watt
 Packing: Individually Sleeved
 36/Master, 12/Inner



3 Way/Mogul

Soft White
 Mogul Base
 120 Volt
S1822 100/300 Watt
 Packing: Individually Sleeved
 12/Master

general service lamps

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------------|-----------------|-------------------|--------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 30 | | | | | | | | 250 | CC-2V | 5 1/16" | Sleeve | 36/12 |
| 70 | A21 | Med. Brass | S1820 | 30/70/100A21/W | White | 120V | 2500 | 700 | C-9 | | | |
| 100 | | | | | | | | 950 | | | | |
| 50 | | | | | | | | 520 | CC-2V | 5 1/16" | Sleeve | 36/12 |
| 100 | A21 | Med. Brass | S1821 | 50/100/150A21/W | White | 120V | 2500 | 1050 | C-9 | | | |
| 150 | | | | | | | | 1570 | | | | |
| 50 | | | | | | | | 640 | CC-8 | 5 1/16" | Sleeve | 12 |
| 200 | A21 | Med. Alum. | S1823 | 50/200/250A21/W | White | 120V | 1200 | 3300 | CC-8 | | | |
| 250 | | | | | | | | 3940 | | | | |
| 100 | | | | | | | | 1385 | CC-8 | | | |
| 200 | PS25 | Mog. Alum. | S1822 | 100/200/300PS25/W | White | 120V | 1200 | 3540 | CC-8 | 6 3/4" | Sleeve | 12 |
| 300 | | | | | | | | 4925 | | | | |

3-Way Household Lamps

Medium Base



BRILLIANT
WHITE
LIGHT

EXTRA
LONG
LIFE!

HALOGEN

Dual halogen capsules create 3 light levels

Not Shown Actual Size



**REDUCED SIZE
A19 3 WAY**

3-Way Halogen Reading Light

A19 3-Way

Soft White/4000 Hours
Medium Base
120 Volt
S4505 30/70/100 Watt
S4506 50/100/150 Watt
Packing: Individually Sleeved
36/Master, 12/Inner

Soft White
Medium Base
120 Volt
S1824 30/70/100 Watt
Packing: Individually Sleeved
36/Master, 12/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Flament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|------------|-----------------|---------------------|--------|-------|------------------|--------|---------|---------|------------|----------------------|
| 30 | | | | | | | | 250 | CC-8 | | | |
| 70 | A19 | Med. Brass | S1824 | 30/70/100A19/W | White | 120V | 2500 | 700 | CC-8 | 4 1/8" | Sleeve | 36/12 |
| 100 | | | | | | | | 950 | | | | |
| 30 | | | | | | | | 295 | CC-8 | | | |
| 70 | A21 | Med. Alum. | S4505 | 30/70/100A21/HAL/W | White | 120V | 4000 | 785 | CC-8 | 5 1/16" | Sleeve | 36/12 |
| 100 | | | | | | | | 1080 | | | | |
| 50 | | | | | | | | 385 | CC-8 | | | |
| 100 | A21 | Med. Alum. | S4506 | 50/100/150A21/HAL/W | White | 120V | 4000 | 1400 | CC-8 | 5 1/16" | Sleeve | 36/12 |
| 150 | | | | | | | | 1985 | | | | |

general service lamps

A21 Household Brass Base



Lamps

2500 HOURS/130 Volt

Medium Base

Not Shown Actual Size



Clear

Medium Base
130 Volt
S3981 150 Watt
Packing:
Individually Boxed
24/Master



Frosted

Medium Base
130 Volt
S3980 150 Watt
Packing:
Individually Boxed
24/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|--|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 150 | A21 | Med. | S3981 | 150A21 | Clear | 130V | 2500 | 1750 | C-9 | 5 1/16" | Box | 24 |
| 150 | A21 | Med. | S3980 | 150A21/F | Frosted | 130V | 2500 | 1750 | C-9 | 5 1/16" | Box | 24 |
| 130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE | | | | | | | | | | | | |
| 134 | A21 | Med. | S3981 | 150A21 | Clear | 130V | 6000 | 1350 | C-9 | 5 1/16" | Box | 24 |
| 134 | A21 | Med. | S3980 | 150A21/F | Frosted | 130V | 6000 | 1350 | C-9 | 5 1/16" | Box | 24 |

general service lamps

2500 Hours / 130 Volt

Lamps

Not Shown Actual Size

Medium Base



Frosted



Clear

Medium Base
130 Volt
S3982 200 Watt
Packing:
Individually Boxed
24/Master

Medium Base
130 Volt
S3983 200 Watt
Packing:
Individually Boxed
24/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|--|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 200 | A23 | Med. | S3983 | 200A23 | Clear | 130V | 2500 | 2500 | C-9 | 6 1/16" | Box | 24 |
| 200 | A23 | Med. | S3982 | 200A23/F | Frosted | 130V | 2500 | 2500 | C-9 | 6 1/16" | Box | 24 |
| 130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE | | | | | | | | | | | | |
| 179 | A23 | Med. | S3983 | 200A23 | Clear | 130V | 6000 | 1750 | C-9 | 6 1/16" | Box | 24 |
| 179 | A23 | Med. | S3982 | 200A23/F | Frosted | 130V | 6000 | 1750 | C-9 | 6 1/16" | Box | 24 |

general service lamps



PS25 General Brass Base



Service Lamps

2500 Hours/130 Volt

Not Shown Actual Size



Clear

Medium Base
300M 130 Volt
S4959 300 Watt
Packing:
Individually Boxed
24/Master



Frosted

Medium Base
300M/IF 130 Volt
S4960 300 Watt
Packing:
Individually Boxed
24/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|-----------------------------------|------------|-----------|
| 300 | PS25 | Med. | S4959 | 300M | Clear | 130V | 2500 | 3600 | C-9 | 6 ¹⁵ / ₁₆ " | Box | 24 |
| 300 | PS25 | Med. | S4960 | 300M/IF | Frosted | 130V | 2500 | 3600 | C-9 | 6 ¹⁵ / ₁₆ " | Box | 24 |

130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE

| | | | | | | | | | | | | |
|-----|------|------|--------------|---------|---------|------|------|------|-----|-----------------------------------|-----|----|
| 264 | PS25 | Med. | S4959 | 300M | Clear | 130V | 5000 | 2640 | C-9 | 6 ¹⁵ / ₁₆ " | Box | 24 |
| 264 | PS25 | Med. | S4960 | 300M/IF | Frosted | 130V | 5000 | 2640 | C-9 | 6 ¹⁵ / ₁₆ " | Box | 24 |

general service lamps

2500 Hours/130 Volt

Service **Lamps**

Not Shown Actual Size



Clear

Mogul Base
300 130 Volt
S4961 300 Watt
Packing:
Individually Boxed
12/Master



Frosted

Mogul Base
300IF 130 Volt
S4962 300 Watt
Packing:
Individually Boxed
12/Master

general service lamps

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------|
| 300 | PS35 | Mog. | S4961 | 300 | Clear | 130V | 2500 | 3600 | C-9 | 9 3/8" | Box | 12 |
| 300 | PS35 | Mog. | S4962 | 300/IF | Frosted | 130V | 2500 | 3600 | C-9 | 9 3/8" | Box | 12 |

130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE

| | | | | | | | | | | | | |
|-----|------|------|--------------|--------|---------|------|------|------|-----|--------|-----|----|
| 264 | PS35 | Mog. | S4961 | 300 | Clear | 130V | 5000 | 2640 | C-9 | 9 3/8" | Box | 12 |
| 264 | PS35 | Mog. | S4962 | 300/IF | Frosted | 130V | 5000 | 2640 | C-9 | 9 3/8" | Box | 12 |

A19 Energy Saver



Lamps Aluminum Base

Medium Base

Not Shown Actual Size



Energy Saver
130 Volt

Frosted
Medium Base

- S4990** 40A/34
- S4991** 60A/52
- S4992** 75A/67
- S4993** 100A/90

Packing: Boxed, 4 Pack,
48/Master, 12 4-Packs



Energy Saver
120 Volt

Frosted
Medium Base

- S4460** 40A/34
- S4461** 60A/52
- S4462** 75A/67
- S4463** 100A/90

Packing: Boxed, 4 Pack,
48/Master, 12 4-Packs

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn. |
|--|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|---------|------------|----------|
| 34 | A19 | Med. | S4990 | 40A/34 | Frosted | 130V | 1500 | 375 | CC-8 | 4 7/16" | Box/4 | 48 |
| 34 | A19 | Med. | S4460 | 40A/34 | Frosted | 120V | 1500 | 385 | CC-8 | 4 7/16" | Box/4 | 48 |
| 52 | A19 | Med. | S4991 | 60A/52 | Frosted | 130V | 1000 | 740 | CC-8 | 4 7/16" | Box/4 | 48 |
| 52 | A19 | Med. | S4461 | 60A/52 | Frosted | 120V | 1000 | 745 | CC-8 | 4 7/16" | Box/4 | 48 |
| 67 | A19 | Med. | S4992 | 75A/67 | Frosted | 130V | 750 | 1065 | CC-8 | 4 7/16" | Box/4 | 48 |
| 67 | A19 | Med. | S4462 | 75A/67 | Frosted | 120V | 750 | 1040 | CC-8 | 4 7/16" | Box/4 | 48 |
| 90 | A19 | Med. | S4993 | 100A/90 | Frosted | 130V | 750 | 1550 | CC-8 | 4 7/16" | Box/4 | 48 |
| 90 | A19 | Med. | S4463 | 100A/90 | Frosted | 120V | 750 | 1520 | CC-8 | 4 7/16" | Box/4 | 48 |
| 130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE | | | | | | | | | | | | |
| 26 | A19 | Med. | S4990 | 40A/34 | Frosted | 130V | 3750 | 285 | CC-8 | 4 7/16" | Box/4 | 48 |
| 46 | A19 | Med. | S4991 | 60A/52 | Frosted | 130V | 3750 | 550 | CC-8 | 4 7/16" | Box/4 | 48 |
| 59 | A19 | Med. | S4992 | 75A/67 | Frosted | 130V | 1875 | 770 | CC-8 | 4 7/16" | Box/4 | 48 |
| 79 | A19 | Med. | S4993 | 100A/90 | Frosted | 130V | 1875 | 1125 | CC-8 | 4 7/16" | Box/4 | 48 |

general service lamps

Linear Incandescent Lamps

Not Shown Actual Size



T8
Medium Base

T8
Disc Base

T8
Disc Base

T10
S14S Base

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|-----------|------------|-----------|
| 40 | T8 | Med. | S2977 | 40T8 | Clear | 130V | 2000 | 265 | C-8 | 12" | Box | 10 |
| 60 | T8 | Med. | S2978 | 60T8 | Clear | 130V | 2000 | 425 | C-8 | 12" | Box | 10 |
| 75 | T8 | Med. | S2979 | 75T8 | Clear | 130V | 2000 | 584 | C-8 | 12" | Box | 10 |
| 40 | T8 | Disc | S2980 | L40 | Clear | 120V | 1500 | 325 | C-8 | 11 3/4" | Sleeve | 24 |
| 40 | T8 | Disc | S2981 | L40W | White | 120V | 1500 | 295 | C-8 | 11 3/4" | Sleeve | 12 |
| 60 | T8 | Disc | S2982 | L60 | Clear | 120V | 1500 | 480 | C-8 | 17 3/4" | Sleeve | 24 |
| 60 | T8 | Disc | S2983 | L60W | White | 120V | 1500 | 450 | C-8 | 17 3/4" | Sleeve | 12 |
| 60 | T10 | S14S | S4894 | LN60 | White | 125V | 1000 | 460 | C-8 | 19 11/16" | Box | 25 |
| 150 | T10 | S14S | S4895 | LN150 | White | 125V | 1000 | 930 | C-8 | 39 1/8" | Sleeve | 16 |

Natural Spectrum

120 Volt / 2000 Hours **Neodymium** Lamps

Natural Spectrum Lamps utilize a rare earth element called Neodymium which is integral to the glass. This element filters out the yellow hue commonly associated with incandescent lamps. Thus creating a truer and more accurate color of light.



B10

Natural Spectrum

Cand. Base

S2970 25 Watt 120V

S2971 40 Watt 120V

S2972 60 Watt 120V

Packing: 1/Card
50/Master, 10/Inner



G16 1/2"

Natural Spectrum

Cand. Base

S2973 25 Watt 120V

S2974 40 Watt 120V

S2975 60 Watt 120V

Packing: 1/Card
50/Master, 10/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|--------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B10 | Cand. | S2970 | C32F25VLX | Frosted | 120V | 2000 | 220 | CC-2V | 3 7/8" | 1/Card | 50/10 |
| 25 | G16 1/2" | Cand. | S2973 | G161/2F25VLX | Frosted | 120V | 2000 | 220 | CC-2V | 3" | 1/Card | 50/10 |
| 40 | B10 | Cand. | S2971 | C32F40VLX | Frosted | 120V | 2000 | 370 | CC-2V | 3 7/8" | 1/Card | 50/10 |
| 40 | G16 1/2" | Cand. | S2974 | G161/2F40VLX | Frosted | 120V | 2000 | 370 | CC-2V | 3" | 1/Card | 50/10 |
| 60 | B10 | Cand. | S2972 | C32F60VLX | Frosted | 120V | 2000 | 650 | CC-2V | 3 7/8" | 1/Card | 50/10 |
| 60 | G16 1/2" | Cand. | S2975 | G161/2F60VLX | Frosted | 120V | 2000 | 650 | CC-2V | 3" | 1/Card | 50/10 |

specialty lamps

Natural Spectrum

Neodymium Lamps 120 Volt / 5000 Hours

Natural Spectrum Lamps utilize a rare earth element called Neodymium which is integral to the glass. This element filters out the yellow hue commonly associated with incandescent lamps. Thus creating a truer and more accurate color of light.



R20

Flood Natural Spectrum

Medium Base

S4824 60 Watt

Packing: Individually Boxed
50/Master, 10/Inner

R30

Flood Natural Spectrum

Medium Base

S4825 75 Watt

S4826 100 Watt

Packing: Individually Boxed
50/Master, 10/Inner

R40

Flood Natural Spectrum

Medium Base

S4827 150 Watt

Packing: Individually Boxed
50/Master, 10/Inner

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 60 | R20 | Med. | S4824 | R20FF60VLX | Frosted | 120V | 5000 | 520 | C-9 | 4" | Box | 50/10 |
| 75 | R30 | Med. | S4825 | R30FF75VLX | Frosted | 120V | 5000 | 680 | C-9 | 5 3/8" | Box | 50/10 |
| 100 | R30 | Med. | S4826 | R30FF100VLX | Frosted | 120V | 5000 | 1000 | C-9 | 5 3/8" | Box | 50/10 |
| 150 | R40 | Med. | S4827 | R40FF150VLX | Frosted | 120V | 5000 | 1450 | C-9 | 6 1/2" | Box | 50/10 |

Natural Spectrum

120 Volt / 5000 Hours **Neodymium** Lamps



specialty lamps

A15/A19

Natural Spectrum
Medium Base

- ** S2976 40 Watt A15 Frosted
 - S4816 60 Watt A19 Frosted
 - S4817 60 Watt A19 Clear
- Packing: Individually Boxed
50/Master, 10/Inner

** Carded

A21

Natural Spectrum
Medium Base

- S4818 75 Watt Frosted
 - S4819 75 Watt Clear
 - S4820 100 Watt Frosted
 - S4821 100 Watt Clear
 - S4822 150 Watt Frosted
- Packing: Individually Boxed
50/Master, 10/Inner

3-Way

Frosted
Natural Spectrum

- Medium Base
S4823 50/100/150 Watt
Packing: Individually Boxed
50/Master, 10/Inner

G25

Frosted
Natural Spectrum

- Medium Base
S4815 40 Watt
Packing: Individually Boxed
50/Master, 10/Inner

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|--------|-----------|------|-----------------|------------|---------|-------|------------------|--------------|----------|---------|------------|-----------------------|
| 40 | A15* | Med. | S2976 | A15F40VLX | Frosted | 120V | 5000 | 300 | C-9 | 3 1/2" | Card/1 | 50/10 |
| 40 | G25 | Med. | S4815 | G25F40VLX | Frosted | 120V | 5000 | 320 | C-9 | 4 3/8" | Box | 50/10 |
| 60 | A19 | Med. | S4816 | A19F60VLX | Frosted | 120V | 5000 | 465 | C-9 | 4 1/8" | Box | 50/10 |
| 60 | A19 | Med. | S4817 | A19C60VLX | Clear | 120V | 5000 | 465 | C-9 | 4 1/8" | Box | 50/10 |
| 75 | A21 | Med. | S4818 | A21F75VLX | Frosted | 120V | 5000 | 630 | C-9 | 5 1/16" | Box | 50/10 |
| 75 | A21 | Med. | S4819 | A21C75VLX | Clear | 120V | 5000 | 630 | C-9 | 5 1/16" | Box | 50/10 |
| 100 | A21 | Med. | S4820 | A21F100VLX | Frosted | 120V | 5000 | 910 | C-9 | 5 1/16" | Box | 50/10 |
| 100 | A21 | Med. | S4821 | A21C100VLX | Clear | 120V | 5000 | 910 | C-9 | 5 1/16" | Box | 50/10 |
| 150 | A21 | Med. | S4822 | A21F150VLX | Frosted | 120V | 5000 | 1400 | C-9 | 5 1/16" | Box | 50/10 |
| 50-150 | A21 | Med. | S4823 | A21F3WVLX | Frosted | 120V | 5000 | 350/910/1260 | C-9 | 5 1/16" | Box | 50/10 |

* Not Shown

Lamps

Satco Shatter Proof Lamps feature a special mylon® coating which effectively contains glass particles should the lamp break.

These lamps are perfect in food storage preparation, display and sorting tables, hospitals, restaurants and recreation facilities.

Special orders are available for large quantities on specific lamp types.



Not Shown Actual Size



A15

A19

A21

A21

Frosted
Medium Base 130V
S4880 25 Watt
S4881 40 Watt
S4882 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

Frosted
Medium Base 130V
S3927 60 Watt
S3928 75 Watt
S3929 100 Watt
Packing: Boxed 2 Pack
24/Master, 12 - 2 Packs
Sold Per Pack

Frosted
Medium Base 130V
S4883 150 Watt
Packing: Indiv. Boxed
24/Master

Rough Service
Medium Base 130V
S3972 75 Watt Frosted
S3973 100 Watt Frosted
Packing: Indiv. Boxed
24/Master

| Watts | Bulb Type | Base | Satco | | Finish | Volts | Avg. Rated | | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|--------------|--------------|---------|-------|------------|--------|----------|---------|------------|-----------------------|
| | | | Order No. | Lamp Code | | | Hours | Lumens | | | | |
| 25 | A15 | Med. | S4880 | 25A15/TF | Frosted | 130V | 2500 | 120 | C-9 | 3 1/2" | Box | 500/25 |
| 40 | A15 | Med. | S4881 | 40A15/TF | Frosted | 130V | 2500 | 280 | C-9 | 3 1/2" | Box | 500/25 |
| 60 | A15 | Med. | S4882 | 60A15/TF | Frosted | 130V | 2500 | 530 | C-9 | 3 1/2" | Box | 500/25 |
| 60 | A19 | Med. | S3927 | 60A19/RS/TF | Frosted | 130V | 5000 | 520 | C-9 | 4 1/8" | 2/Pks | 12 |
| 75 | A19 | Med. | S3928 | 75A19/RS/TF | Frosted | 130V | 5000 | 680 | C-9 | 4 1/8" | 2/Pks | 12 |
| 100 | A19 | Med. | S3929 | 100A19/RS/TF | Frosted | 130V | 5000 | 960 | C-9 | 4 1/8" | 2/Pks | 12 |
| 75 | A21 | Med. | S3972 | 75A21/TF | Frosted | 130V | 2500 | 620 | C-9 | 5 5/16" | Box | 24 |
| 100 | A21 | Med. | S3973 | 100A21/TF | Frosted | 130V | 2500 | 880 | C-9 | 5 5/16" | Box | 24 |
| 150 | A21 | Med. | S4883 | 150A21/TF | Frosted | 130V | 2500 | 1750 | C-9 | 5 5/16" | Box | 24 |



specialty lamps

| 250R40/HR | 250R40/1 | BR30 | R20 |
|---|---|--|--|
| Red Heat Lamp Medium Base 120V S4884 250 Watt Packing: Indiv. Sleeved 12/Master | Clear Heat Lamp Medium Base 120V S4885 250 Watt Packing: Indiv. Sleeved 12/Master | Medium Base 120V S4887 65 Watt Packing: Indiv. Sleeved 96/Master, 12/Inner | Medium Base 120V S4886 50 Watt Packing: Indiv. Sleeved 96/Master, 12/Inner |

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|--------------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 50 | R20 | Med. | S4886 | 50R20/TF | Frost. | 120V | 2000 | 375 | C-9 | 4" | Sleeve | 96/12 |
| 65 | BR30 | Med. | S4887 | 65BR30/TF | Frost. | 120V | 2000 | 685 | C-9 | 5 3/8" | Sleeve | 96/12 |
| 250 | R40 | Med. | S4885 | 250R40/1/TF | Clear | 120V | 5000 | n/a | C-9 | 6 7/8" | Sleeve | 12 |
| 250 | R40 | Med. | S4884 | 250R40/HR/TF | Red | 120V | 5000 | n/a | C-9 | 6 7/8" | Sleeve | 12 |

Low Voltage *Brass Base*



Lamps

1500 Hours

Not Shown Actual Size



12 Volt

Frosted

Medium Base

S5010 25 Watt/A19

S5011 50 Watt/A19

S5012 75 Watt/A21

S5013 100 Watt/A21

Packing: Sleeve, 1 Pack,
120 Master, 6/Inner



34 Volt

Frosted

Medium Base

S5020 25 Watt/A19

S5021 50 Watt/A19

S5022 75 Watt/A21

S5023 100 Watt/A21

Packing: Sleeve, 1 Pack,
120 Master, 6/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|------------|--------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 25 | A19 | Med. | S5010 | 25A19/12V | Frost | 12V | 1500 | 250 | C-6 | 4 1/8" | Sleeve | 120/6 |
| 50 | A19 | Med. | S5011 | 50A19/12V | Frost | 12V | 1500 | 540 | C-6 | 4 1/8" | Sleeve | 120/6 |
| 75 | A21 | Med. | S5012 | 75A21/12V | Frost | 12V | 1500 | 720 | C-6 | 5 5/16" | Sleeve | 120/6 |
| 100 | A21 | Med. | S5013 | 100A21/12V | Frost | 12V | 1500 | 980 | C-6 | 5 5/16" | Sleeve | 120/6 |
| 25 | A19 | Med. | S5020 | 25A19/34V | Frost | 34V | 1500 | 250 | C-6 | 4 1/8" | Sleeve | 120/6 |
| 50 | A19 | Med. | S5021 | 50A19/34V | Frost | 34V | 1500 | 540 | C-6 | 4 1/8" | Sleeve | 120/6 |
| 75 | A21 | Med. | S5022 | 75A21/34V | Frost | 34V | 1500 | 720 | C-6 | 5 5/16" | Sleeve | 120/6 |
| 100 | A21 | Med. | S5023 | 100A21/34V | Frost | 34V | 1500 | 990 | C-6 | 5 5/16" | Sleeve | 120/6 |

Not Shown Actual Size



A19/130V

Frosted
Euro D.C. Base
130 Volt
S5030 40 Watt
S5031 60 Watt

Packing: Indiv. Boxed
120/Master

A19/230V

Frosted
Euro D.C. Base
230 Volt
S5040 40 Watt
S5041 60 Watt



A19/220V

Soft White
Medium Base/220 Volt
S4076 40 Watt **S4078** 75 Watt
S4077 60 Watt **S4079** 100 Watt
Packing: Individually Boxed
120/Master

Halogen - J Type Double Ended



220 Volt
S3185 500 Watt T3Q/CL 118mm
Packing: Individually Boxed
12/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-----------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 40 | A19 | Med. | S4076 | 40A19/F | Frost | 220V | 2500 | 330 | CC-2F | 4 1/8" | Box | 120 |
| 60 | A19 | Med. | S4077 | 60A19/F | Frost | 220V | 2500 | 630 | CC-2F | 4 1/8" | Box | 120 |
| 75 | A19 | Med. | S4078 | 75A19/F | Frost | 220V | 2500 | 750 | CC-2F | 4 1/8" | Box | 120 |
| 100 | A19 | Med. | S4079 | 100A19/F | Frost | 220V | 2500 | 1250 | CC-2F | 4 1/8" | Box | 120 |
| 40 | A19 | Euro D.C. | S5030 | 40A19/F | Frost | 130V | 2500 | 330 | CC-6 | 4 1/8" | Box | 120 |
| 40 | A19 | Euro D.C. | S5040 | 40A19/F | Frost | 230V | 2500 | 330 | CC-2F | 4 1/8" | Box | 120 |
| 60 | A19 | Euro D.C. | S5031 | 60A19/F | Frost | 130V | 2500 | 630 | CC-6 | 4 1/8" | Box | 120 |
| 60 | A19 | Euro D.C. | S5041 | 60A19/F | Frost | 230V | 2500 | 630 | CC-2F | 4 1/8" | Box | 120 |
| 500 | T3 | R7S | S3185 | 500T3Q/CL | Clear | 220V | 2000 | 9500 | C-8 | 4 11/16" | Box | 220 |

220 Volt Brass Base



Globe Lights G25 3 1/8"

2500 Hours

Clear

Medium Base
(220 Volt)

A3644 40 Watt

Packing: Individually
Boxed
72/Master, 6/Inner



Shown
Actual Size



White

Medium Base
(220 Volt)

A3645 40 Watt

Packing: Individually Boxed
72/Master, 6/Inner



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 40 | G25 | Med. | A3644 | 40G25 | Clear | 220V | 2500 | 212 | CC-9 | 4 3/8" | Box | 72/6 |
| 40 | G25 | Med. | A3645 | 40G25/W | White | 220V | 2500 | 187 | CC-9 | 4 3/8" | Box | 72/6 |

Decorative Torpedo Bulbs

Bulbs



specialty lamps



Clear

E14 Euro Base
220 Volt
S3393 25 Watt
S3394 40 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Clear

E12 Cand. Base
220 Volt
S3386 25 Watt
S3387 40 Watt
S3388 60 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Frosted

E12 Cand. Base
220 Volt
S3385 40 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner



Clear

Medium Base
220 Volt
S3384 40 Watt
Packing: Indiv. Boxed
500/Master, 25/Inner

Bulbs Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-----------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B10 | E12/Cand. | S3386 | 25B10 | Clear | 220V | 1000 | 200 | CC-2F | 3 3/4" | Box | 500/25 |
| 25 | B10 | E14/Euro. | S3393 | 25B10 | Clear | 220V | 1000 | 200 | CC-2F | 3 3/4" | Box | 500/25 |
| 40 | B10 | E12/Cand. | S3385 | 40B10/F | Frost. | 220V | 1000 | 330 | CC-2F | 3 3/4" | Box | 500/25 |
| 40 | B10 | E12/Cand. | S3387 | 40B10 | Clear | 220V | 1000 | 330 | CC-2F | 3 3/4" | Box | 500/25 |
| 40 | B10 | E14/Euro. | S3394 | 40B10 | Clear | 220V | 1000 | 330 | CC-2F | 3 3/4" | Box | 500/25 |
| 40 | B11 | Medium | S3384 | 40B11 | Clear | 220V | 1000 | 370 | CC-2F | 3 7/8" | Box | 500/25 |
| 60 | B10 | E12/Cand. | S3388 | 60B10 | Clear | 220V | 1000 | 650 | CC-2F | 3 3/4" | Box | 500/25 |

230 Volt Brass Base



BR38 Weather-Proof Reflectors

Not Shown Actual Size

2000 Hours

BR38 Colors

Medium Base
230 Volt

- S5002** 100 Watt Red
- S5003** 100 Watt Amber
- S5004** 100 Watt Yellow
- S5005** 100 Watt Green
- S5006** 100 Watt Blue
- S5007** 100 Watt Pink

Packing: Individually Boxed
6/Master

BR38 Clear

Medium Base
230 Volt

- S5000** 75 Watt Flood
- S5001** 150 Watt Flood

Packing: Individually Boxed
12/Master



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|----------|-----------------|------------|--------|-------|------------------|--------|----------|---------|------------|-----------|
| 75 | BR38 | E27/Med. | S5000 | 75BR38/FL | Clear | 230V | 2000 | 750 | CC9 | 5 5/16" | Box | 12 |
| 100 | BR38 | E27/Med. | S5002 | 100BR38/R | Red | 230V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | E27/Med. | S5003 | 100BR38/A | Amber | 230V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | E27/Med. | S5004 | 100BR38/Y | Yellow | 230V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | E27/Med. | S5005 | 100BR38/G | Green | 230V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | E27/Med. | S5006 | 100BR38/B | Blue | 230V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 100 | BR38 | E27/Med. | S5007 | 100BR38/PK | Pink | 230V | 2000 | n/a | CC9 | 5 5/16" | Box | 6 |
| 150 | BR38 | E27/Med. | S5001 | 150BR38/FL | Clear | 230V | 2000 | 1550 | CC9 | 5 5/16" | Box | 12 |

specialty lamps

Halogen



PAR16/PAR20/PAR30

Whiter light, brighter colors, precise beam control.

Not Shown Actual Size



PAR16

PAR20

PAR30

SATCO PAR HALOGEN LAMPS QUALITY • VALUE • PERFORMANCE

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------------|---------|-------|------------------|-------|--------|----------|---------|------------|-----------|
| 45 | PAR16 | Med. | S2200 | 45PAR16/HAL/NFL | NFL 30° | 120V | 2500 | 1200 | 420 | CC-8 | 3 3/16" | Box | 15 |
| 45 | PAR16 | Med. | S2300 | 45PAR16/HAL/NFL | NFL 30° | 130V | 2500 | 1200 | 420 | CC-8 | 3 3/16" | Box | 15 |
| 60 | PAR16 | Med. | S2201 | 60PAR16/HAL/NFL | NFL 30° | 120V | 2500 | 1400 | 600 | CC-8 | 3 3/16" | Box | 15 |
| 60 | PAR16 | Med. | S2301 | 60PAR16/HAL/NFL | NFL 30° | 130V | 2500 | 1400 | 600 | CC-8 | 3 3/16" | Box | 15 |
| 60 | PAR16 | Med. | S2202 | 60PAR16/HAL/NSP | NSP 10° | 120V | 2500 | 4700 | 550 | CC-8 | 3 3/16" | Box | 15 |
| 60 | PAR16 | Med. | S2302 | 60PAR16/HAL/NSP | NSP 10° | 130V | 2500 | 4700 | 550 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S2203 | 75PAR16/HAL/NFL | NFL 30° | 120V | 2500 | 1800 | 850 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S2303 | 75PAR16/HAL/NFL | NFL 30° | 130V | 2500 | 1800 | 850 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S2204 | 75PAR16/HAL/NSP | NSP 10° | 120V | 2500 | 7000 | 850 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S2304 | 75PAR16/HAL/NSP | NSP 10° | 130V | 2500 | 7000 | 850 | CC-8 | 3 3/16" | Box | 15 |
| 50 | PAR20 | Med. | S2205 | 50PAR20/HAL/NFL | NFL 34° | 120V | 2500 | 1300 | 495 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S2305 | 50PAR20/HAL/NFL | NFL 34° | 130V | 2500 | 1300 | 495 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S2206 | 50PAR20/HAL/NSP | NSP 10° | 120V | 2500 | 4700 | 495 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S2306 | 50PAR20/HAL/NSP | NSP 10° | 130V | 2500 | 4700 | 495 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR30 | Med. | S2207 | 50PAR30/HAL/NFL | NFL 34° | 120V | 2500 | 1750 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2307 | 50PAR30/HAL/NFL | NFL 34° | 130V | 2500 | 1750 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2208 | 50PAR30/HAL/WFL | WFL 50° | 120V | 2500 | 460 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2308 | 50PAR30/HAL/WFL | WFL 50° | 130V | 2500 | 460 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2209 | 50PAR30/HAL/NSP | NSP 9° | 120V | 2500 | 7600 | 560 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S2309 | 50PAR30/HAL/NSP | NSP 9° | 130V | 2500 | 7600 | 56+0 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2210 | 75PAR30/HAL/NFL | NFL 34° | 120V | 2500 | 3100 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2310 | 75PAR30/HAL/NFL | NFL 34° | 130V | 2500 | 3100 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2211 | 75PAR30/HAL/WFL | WFL 50° | 120V | 2500 | 770 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2311 | 75PAR30/HAL/WFL | WFL 50° | 130V | 2500 | 770 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2212 | 75PAR30/HAL/NSP | NSP 9° | 120V | 2500 | 13000 | 945 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S2312 | 75PAR30/HAL/NSP | NSP 9° | 130V | 2500 | 13000 | 945 | CC-8 | 3 5/8" | Box | 15 |

halogen lamps

Not Shown Actual Size



PAR38

PAR30LN

SATCO PAR HALOGEN LAMPS

QUALITY • VALUE • PERFORMANCE

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP* | Lumens | Filament | M.O.L. | Pack Type | Mst. Ctn. |
|-------|-----------|------|-----------------|------------------|---------|-------|------------------|-------|--------|----------|---------|-----------|-----------|
| 50 | PAR30/LN | Med. | S2213 | 50PAR30/HAL/NFL | NFL 34° | 120V | 2500 | 1750 | 560 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2313 | 50PAR30/HAL/NFL | NFL 34° | 130V | 2500 | 1750 | 560 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2214 | 50PAR30/HAL/WFL | WFL 50° | 120V | 2500 | 460 | 560 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2314 | 50PAR30/HAL/WFL | WFL 50° | 130V | 2500 | 460 | 560 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2215 | 50PAR30/HAL/NSP | NSP 9° | 120V | 2500 | 7600 | 550 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S2315 | 50PAR30/HAL/NSP | NSP 9° | 130V | 2500 | 7600 | 550 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2216 | 75PAR30/HAL/NFL | NFL 34° | 120V | 2500 | 3100 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2316 | 75PAR30/HAL/NFL | NFL 34° | 130V | 2500 | 3100 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2217 | 75PAR30/HAL/WFL | WFL 50° | 120V | 2500 | 770 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2317 | 75PAR30/HAL/WFL | WFL 50° | 130V | 2500 | 770 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2218 | 75PAR30/HAL/NSP | NSP 9° | 120V | 2500 | 13000 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S2318 | 75PAR30/HAL/NSP | NSP 9° | 130V | 2500 | 13000 | 945 | CC-8 | 4 1/2" | Box | 15 |
| 45 | PAR38 | Med. | S2219 | 45PAR38/HAL/FL | FL 30° | 120V | 2500 | 1380 | 465 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. | S2319 | 45PAR38/HAL/FL | FL 30° | 130V | 2500 | 1380 | 465 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. | S2220 | 45PAR38/HAL/NSP | NSP 9° | 120V | 2500 | 5000 | 465 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. | S2320 | 45PAR38/HAL/NSP | NSP 9° | 130V | 2500 | 5000 | 465 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. | S2221 | 75PAR38/HAL/FL | FL 30° | 120V | 2500 | 3200 | 960 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. | S2321 | 75PAR38/HAL/FL | FL 30° | 130V | 2500 | 3200 | 960 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. | S2222 | 75PAR38/HAL/NSP | NSP 9° | 120V | 2500 | 16000 | 960 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. | S2322 | 75PAR38/HAL/NSP | NSP 9° | 130V | 2500 | 16000 | 960 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. | S2223 | 90PAR38/HAL/FL | FL 30° | 120V | 2500 | 3800 | 1260 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. | S2323 | 90PAR38/HAL/FL | FL 30° | 130V | 2500 | 3800 | 1260 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. | S2224 | 90PAR38/HAL/NSP | NSP 9° | 120V | 2500 | 14000 | 1260 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. | S2324 | 90PAR38/HAL/NSP | NSP 9° | 130V | 2500 | 14000 | 1260 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. | S2225 | 120PAR38/HAL/FL | FL 30° | 120V | 2500 | 4700 | 1600 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. | S2325 | 120PAR38/HAL/FL | FL 30° | 130V | 2500 | 4700 | 1600 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. | S2226 | 120PAR38/HAL/NSP | NSP 9° | 120V | 2500 | 22000 | 1600 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. | S2326 | 120PAR38/HAL/NSP | NSP 9° | 130V | 2500 | 22000 | 1600 | CC-8 | 5 5/16" | Box | 15 |

Halogen s

PAR14/PAR16/PAR20

Not Shown Actual Size



PAR14

PAR16

PAR20

Whiter light, brighter colors,
precise beam control.

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------------|---------|-------|------------------|------|--------|----------|---------|------------|-----------|
| 35 | PAR14 | Med. | S4658 | 35PAR14/CAP/WFL | WFL 50° | 120V | 2000 | 85 | 300 | CC-8 | 2 7/16" | Box | 6 |
| 60 | PAR16 | Med. | S4900 | 60PAR16/CAP/NFL | NFL 30° | 120V | 2000 | 1300 | 650 | CC-8 | 2 7/8" | Box | 15 |
| 60 | PAR16 | Med. | S4901 | 60PAR16/CAP/NFL | NFL 30° | 130V | 2000 | 1300 | 650 | CC-8 | 2 7/8" | Box | 15 |
| 60 | PAR16 | Med. | S4902 | 60PAR16/CAP/NSP | NSP 10° | 120V | 2000 | 5000 | 650 | CC-8 | 2 7/8" | Box | 15 |
| 60 | PAR16 | Med. | S4903 | 60PAR16/CAP/NSP | NSP 10° | 130V | 2000 | 5000 | 650 | CC-8 | 2 7/8" | Box | 15 |
| 75 | PAR16 | Med. | S4904 | 75PAR16/CAP/NFL | NFL 30° | 120V | 2000 | 1900 | 900 | CC-8 | 2 7/8" | Box | 15 |
| 75 | PAR16 | Med. | S4905 | 75PAR16/CAP/NFL | NFL 30° | 130V | 2000 | 1900 | 900 | CC-8 | 2 7/8" | Box | 15 |
| 75 | PAR16 | Med. | S4906 | 75PAR16/CAP/NSP | NSP 10° | 120V | 2000 | 7500 | 900 | CC-8 | 2 7/8" | Box | 15 |
| 75 | PAR16 | Med. | S4907 | 75PAR16/CAP/NSP | NSP 10° | 130V | 2000 | 7500 | 900 | CC-8 | 2 7/8" | Box | 15 |
| 35 | PAR20 | Med. | S4908 | 35PAR20/CAP/NFL | NFL 30° | 120V | 2500 | 800 | 360 | CC-8 | 3 1/4" | Box | 15 |
| 35 | PAR20 | Med. | S4663 | 35PAR20/CAP/NFL | NFL 30° | 130V | 2500 | 800 | 360 | CC-8 | 3 1/4" | Box | 15 |
| 35 | PAR20 | Med. | S4909 | 35PAR20/CAP/NSP | NSP 10° | 120V | 2500 | 3000 | 360 | CC-8 | 3 1/4" | Box | 15 |
| 35 | PAR20 | Med. | S4661 | 35PAR20/CAP/NSP | NSP 10° | 130V | 2500 | 3000 | 360 | CC-8 | 3 1/4" | Box | 15 |
| 35 | PAR20 | Med. | S4910 | 35PAR20/CAP/WFL | WFL 40° | 120V | 2500 | 500 | 360 | CC-8 | 3 1/8" | Box | 15 |
| 35 | PAR20 | Med. | S4665 | 35PAR20/CAP/WFL | WFL 40° | 130V | 2500 | 500 | 360 | CC-8 | 3 1/8" | Box | 15 |
| 50 | PAR20 | Med. | S4911 | 50PAR20/CAP/NFL | NFL 30° | 120V | 2500 | 1400 | 550 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S4912 | 50PAR20/CAP/NFL | NFL 30° | 130V | 2500 | 1400 | 550 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S4913 | 50PAR20/CAP/NSP | NSP 10° | 120V | 2500 | 6200 | 550 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S4914 | 50PAR20/CAP/NSP | NSP 10° | 130V | 2500 | 6200 | 550 | CC-8 | 3 1/4" | Box | 15 |
| 50 | PAR20 | Med. | S4666 | 50PAR20/CAP/WFL | WFL 40° | 120V | 2500 | 900 | 550 | CC-8 | 3 1/8" | Box | 15 |

Halogen **PAR30** Short & Long Neck

Not Shown Actual Size



PAR30

Long Neck

PAR30

Short Neck

Whiter light, brighter colors, precise beam control.

SHORT NECK

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP* | Lumens | Filament | M.O.L. | Pack type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------------|---------|-------|------------------|-------|--------|----------|--------|-----------|-----------|
| 50 | PAR30 | Med. | S4915 | 50PAR30/CAP/FL | FL 40° | 120V | 2500 | 1300 | 600 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4916 | 50PAR30/CAP/FL | FL 40° | 130V | 2500 | 1300 | 600 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4917 | 50PAR30/CAP/NFL | NFL 25° | 120V | 2500 | 2300 | 660 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4918 | 50PAR30/CAP/NFL | NFL 25° | 130V | 2500 | 2300 | 660 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4919 | 50PAR30/CAP/NSP | NSP 9° | 120V | 2500 | 8800 | 660 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4920 | 50PAR30/CAP/NSP | NSP 9° | 130V | 2500 | 8800 | 660 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4921 | 75PAR30/CAP/FL | FL 40° | 120V | 2500 | 2000 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4922 | 75PAR30/CAP/FL | FL 40° | 130V | 2500 | 2000 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4923 | 75PAR30/CAP/NFL | NFL 25° | 120V | 2500 | 4000 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4924 | 75PAR30/CAP/NFL | NFL 25° | 130V | 2500 | 4000 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4925 | 75PAR30/CAP/NSP | NSP 9° | 120V | 2500 | 15400 | 1130 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4926 | 75PAR30/CAP/NSP | NSP 9° | 130V | 2500 | 15400 | 1130 | CC-8 | 3 5/8" | Box | 15 |

LONG NECK

| | | | | | | | | | | | | | |
|----|----------|------|--------------|-------------------|---------|------|------|-------|------|------|--------|-----|----|
| 35 | PAR30/LN | Med. | S2654 | 35PAR30LN/CAP/WFL | WFL 50° | 120V | 2500 | 450 | 450 | CC-8 | 4 5/8" | Box | 15 |
| 35 | PAR30/LN | Med. | S2655 | 35PAR30LN/CAP/NSP | NSP 9° | 120V | 2500 | 5700 | 450 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4927 | 50PAR30LN/CAP/WFL | WFL 50° | 120V | 2500 | 660 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4928 | 50PAR30LN/CAP/WFL | WFL 50° | 130V | 2500 | 660 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4929 | 50PAR30LN/CAP/NFL | NFL 25° | 120V | 2500 | 2300 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4930 | 50PAR30LN/CAP/NFL | NFL 25° | 130V | 2500 | 2300 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4931 | 50PAR30LN/CAP/NSP | NSP 9° | 120V | 2500 | 8800 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4932 | 50PAR30LN/CAP/NSP | NSP 9° | 130V | 2500 | 8800 | 660 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4933 | 75PAR30LN/CAP/WFL | WFL 50° | 120V | 2500 | 1100 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4934 | 75PAR30LN/CAP/WFL | WFL 50° | 130V | 2500 | 1100 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4935 | 75PAR30LN/CAP/NFL | NFL 25° | 120V | 2500 | 4000 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4936 | 75PAR30LN/CAP/NFL | NFL 25° | 130V | 2500 | 4000 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4937 | 75PAR30LN/CAP/NSP | NSP 9° | 120V | 2500 | 15400 | 1130 | CC-8 | 4 5/8" | Box | 15 |
| 75 | PAR30/LN | Med. | S4938 | 75PAR30LN/CAP/NSP | NSP 9° | 130V | 2500 | 15400 | 1130 | CC-8 | 4 5/8" | Box | 15 |

Halogen

PAR38



Not Shown Actual Size



Whiter light,
brighter colors,
precise beam
control.

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP* | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|-----------|-----------------|----------------|---------|-------|------------------|-------|--------|----------|---------|------------|-----------|
| 45 | PAR38 | Med. Skt. | S4939 | 45PAR/CAP/FL | FL 30° | 120V | 2500 | 1500 | 560 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. Skt. | S4940 | 45PAR/CAP/FL | FL 30° | 130V | 2500 | 1500 | 560 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. Skt. | S4941 | 45PAR/CAP/NSP | NSP 9° | 120V | 2500 | 10000 | 560 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. Skt. | S4942 | 45PAR/CAP/NSP | NSP 9° | 130V | 2500 | 10000 | 560 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. Skt. | S4630 | 45PAR/CAP/WFL | WFL 50° | 130V | 2500 | 700 | 560 | CC-8 | 5 5/16" | Box | 15 |
| 60 | PAR38 | Med. Skt. | S4943 | 60PAR/CAP/FL | FL 30° | 120V | 3000 | 2500 | 850 | CC-8 | 5 5/16" | Box | 15 |
| 60 | PAR38 | Med. Skt. | S4944 | 60PAR/CAP/FL | FL 30° | 130V | 3000 | 2500 | 850 | CC-8 | 5 5/16" | Box | 15 |
| 60 | PAR38 | Med. Skt. | S4945 | 60PAR/CAP/NSP | NSP 9° | 120V | 3000 | 16000 | 850 | CC-8 | 5 5/16" | Box | 15 |
| 60 | PAR38 | Med. Skt. | S4946 | 60PAR/CAP/NSP | NSP 9° | 130V | 3000 | 16000 | 850 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. Skt. | S4964 | 75PAR/CAP/FL | FL 30° | 120V | 2500 | 3150 | 1060 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. Skt. | S4965 | 75PAR/CAP/FL | FL 30° | 130V | 2500 | 3150 | 1060 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. Skt. | S4966 | 75PAR/CAP/NSP | NSP 9° | 120V | 2500 | 19200 | 1060 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. Skt. | S4967 | 75PAR/CAP/NSP | NSP 9° | 130V | 2500 | 19200 | 1060 | CC-8 | 5 5/16" | Box | 15 |
| 75 | PAR38 | Med. Skt. | S4631 | 75PAR/CAP/WFL | WFL 50° | 130V | 2500 | 1300 | 1060 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4968 | 90PAR/CAP/FL | FL 30° | 120V | 2500 | 3500 | 1310 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4969 | 90PAR/CAP/FL | FL 30° | 130V | 2500 | 3500 | 1310 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4970 | 90PAR/CAP/NSP | NSP 9° | 120V | 2500 | 19000 | 1310 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4971 | 90PAR/CAP/NSP | NSP 9° | 130V | 2500 | 19000 | 1310 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4950 | 90PAR/CAP/WSP | WSP 12° | 120V | 2500 | 14300 | 1310 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4951 | 90PAR/CAP/WSP | WSP 12° | 130V | 2500 | 14300 | 1310 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4632 | 90PAR/CAP/NFL | NFL 25° | 130V | 2500 | 4700 | 1310 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4633 | 90PAR/CAP/WFL | WFL 50° | 130V | 2500 | 1600 | 1310 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. Skt. | S4972 | 120PAR/CAP/FL | FL 30° | 120V | 3000 | 4600 | 1800 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. Skt. | S4973 | 120PAR/CAP/FL | FL 30° | 130V | 3000 | 4600 | 1800 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. Skt. | S4974 | 120PAR/CAP/SP | SP 10° | 120V | 3000 | 22500 | 1800 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. Skt. | S4975 | 120PAR/CAP/SP | SP 10° | 130V | 3000 | 22500 | 1800 | CC-8 | 5 5/16" | Box | 15 |
| 120 | PAR38 | Med. Skt. | S4634 | 120PAR/CAP/WFL | WFL 50° | 130V | 3000 | 2000 | 1800 | CC-8 | 5 5/16" | Box | 15 |
| 250 | PAR38 | Med. Skt. | S4947 | 250PAR/CAP/FL | FL 30° | 120V | 4500 | 4500 | 3600 | CC-8 | 5 5/16" | Box | 6 |
| 250 | PAR38 | Med. Skt. | S4948 | 250PAR/CAP/SP | SP 10° | 120V | 4500 | 46500 | 3600 | CC-8 | 5 5/16" | Box | 6 |

halogen lamps

SATCO® SOFTRAY™ PAR Reflectors

Not Shown Actual Size

PAR16/PAR20/PAR30/PAR38



Frosted Halogen Lamps

S O F T - R A Y

Introducing – Soft Ray , a new concept in halogen lighting. Our new line of frosted MR16 and PAR lamps offer a simple, cost effective solution to problems normally associated with standard halogen reflectors.

It is known that many users of traditional MR16 & PAR lamps object to the “headlamp look” or glary appearance of these lamps. Soft Ray lamps solve these problems and more!

- Glare Free
- Does not create hot spots
- Eliminates shadows & striations
- Produces a smooth and even beam pattern



PAR16



PAR20



PAR30 Short Neck



PAR30 Long Neck



PAR38

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|-----------|-----------------|---------------------|-----------|-------|------------------|--------|----------|---------|------------|-----------|
| 60 | PAR16 | Med. | S4108 | 60PAR16/FL/FROST | Flood 38° | 120V | 2500 | 525 | CC-8 | 3 3/16" | Box | 15 |
| 75 | PAR16 | Med. | S4109 | 75PAR16/FL/FROST | Flood 38° | 120V | 2500 | 725 | CC-8 | 3 3/16" | Box | 15 |
| 50 | PAR20 | Med. | S4100 | 50PAR20/NFL/FROST | Flood 38° | 120V | 2500 | 450 | CC-8 | 3 3/8" | Box | 15 |
| 50 | PAR20 | Med. | S4200 | 50PAR20/NFL/FROST | Flood 38° | 130V | 2500 | 450 | CC-8 | 3 3/8" | Box | 15 |
| 50 | PAR30 | Med. | S4101 | 50PAR30/FL/FROST | Flood 38° | 120V | 2500 | 520 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30 | Med. | S4201 | 50PAR30/FL/FROST | Flood 38° | 130V | 2500 | 520 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4102 | 75PAR30/FL/FROST | Flood 38° | 120V | 2500 | 900 | CC-8 | 3 5/8" | Box | 15 |
| 75 | PAR30 | Med. | S4202 | 75PAR30/FL/FROST | Flood 38° | 130V | 2500 | 900 | CC-8 | 3 5/8" | Box | 15 |
| 50 | PAR30/LN | Med. | S4103 | 50PAR30/LN/FL/FROST | Flood 38° | 120V | 2500 | 520 | CC-8 | 4 1/2" | Box | 15 |
| 50 | PAR30/LN | Med. | S4203 | 50PAR30/LN/FL/FROST | Flood 38° | 130V | 2500 | 520 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S4104 | 75PAR30/LN/FL/FROST | Flood 38° | 120V | 2500 | 900 | CC-8 | 4 1/2" | Box | 15 |
| 75 | PAR30/LN | Med. | S4204 | 75PAR30/LN/FL/FROST | Flood 38° | 130V | 2500 | 900 | CC-8 | 4 1/2" | Box | 15 |
| 45 | PAR38 | Med. Skt. | S4105 | 45PAR38/FL/FROST | Flood 38° | 120V | 2500 | 450 | CC-8 | 5 5/16" | Box | 15 |
| 45 | PAR38 | Med. Skt. | S4205 | 45PAR38/FL/FROST | Flood 38° | 130V | 2500 | 450 | CC-8 | 5 5/16" | Box | 15 |
| 60 | PAR38 | Med. Skt. | S4106 | 60PAR38/FL/FROST | Flood 38° | 120V | 2500 | 600 | CC-8 | 5 5/16" | Box | 15 |
| 60 | PAR38 | Med. Skt. | S4206 | 60PAR38/FL/FROST | Flood 38° | 130V | 2500 | 600 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4107 | 90PAR38/FL/FROST | Flood 38° | 120V | 2500 | 1150 | CC-8 | 5 5/16" | Box | 15 |
| 90 | PAR38 | Med. Skt. | S4207 | 90PAR38/FL/FROST | Flood 38° | 130V | 2500 | 1150 | CC-8 | 5 5/16" | Box | 15 |

halogen lamps

Halogen Reflectors



R20/BR30 & BR40

2500 Hours

- Nickel Plated Brass Base
- High Lumen Output
- Brilliant White Light
- Better Color Rendering than Standard Floods
- 20% Brighter & Longer Lasting



halogen lamps

| R20 | BR30 | BR40 |
|--|--|---|
| Medium Base 120 Volt S4500 50 Watt Packing: Individually Sleeved 48/Master, 6/Inner | Medium Base 120 Volt/130Volt S4501 60 Watt S4401 60 Watt/130 Volt S4502 75 Watt S4402 75 Watt/130 Volt Packing: Individually Sleeved 48/Master, 6/Inner | Medium Base 120 Volt S4504 75 Watt S4503 100 Watt Packing: Individually Sleeved 24/Master, 6/Inner |

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Lumens | Kelvin | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|----------------|------|-------|------------------|--------|--------|--------|------------|-----------------------|
| 50 | R20 | Med. | S4500 | 50R20/FL/HAL | 70° | 120V | 2500 | 480 | 3000K | 4" | Sleeve | 6/48 |
| 60 | BR30 | Med. | S4501 | 60BR30/FL/HAL | 80° | 120V | 2500 | 730 | 3000K | 5 3/8" | Sleeve | 6/48 |
| 60 | BR30 | Med. | S4401 | 60BR30/FL/HAL | 80° | 130V | 2500 | 730 | 3000K | 5 3/8" | Sleeve | 6/48 |
| 75 | BR30 | Med. | S4502 | 75BR30/FL/HAL | 80° | 120V | 2500 | 900 | 3000K | 5 3/8" | Sleeve | 6/48 |
| 75 | BR30 | Med. | S4402 | 75BR30/FL/HAL | 80° | 130V | 2500 | 900 | 3000K | 5 3/8" | Sleeve | 6/48 |
| 75 | BR40 | Med. | S4504 | 75BR40/FL/HAL | 90° | 120V | 2500 | 900 | 3000K | 6 1/2" | Sleeve | 6/24 |
| 100 | BR40 | Med. | S4503 | 100BR40/FL/HAL | 90° | 120V | 2500 | 1400 | 3000K | 6 1/2" | Sleeve | 6/24 |

All lamps rated at design voltage.

2000 Hours / 12 & 24 Volt **MR8 & MR11** Lamps

Not Shown
Actual Size

MR8 Lensed

12 Volt
S4646 10W NSP
S4645 10W NFL
Packing: Individually Boxed,
12/Carton



MR11 Bayonet / Lensed

12 Volt
S1954 20W SP FST/C
S1952 20W NFL FSV/C
S1955 35W SP GDY/C
S1953 35W NFL GDZ/C

Packing: Individually Boxed
12/Carton



MR11 12 Volt

S3194 5W NSP
S3195 10W SP
S3150 20W NSP FTB
S3152 20W SP FTC
S3154 20W NFL FTD
S3151 35W NSP FTE
S3153 35W SP FTF
S3155 35W NFL FTH

Packing: Individually Boxed,
12/Carton



MR11 Frosted GZ4 / Lensed

12 Volt
S4124 20W FL
S4125 35W FL
Packing: Individually Boxed
12/Carton



MR11 Lensed

12 Volt
S1950 20W NFL FTD/C
S1951 35W NFL FTH/C
24 Volt
S1990 20W NSP FTD/C
S1988 20W NFL FTD/C
S1991 35W NSP FTH/C
S1989 35W NFL FTH/C
Packing: Individually Boxed,
12/Carton



| Watts | Bulb Type | Base | Satco Order No. | ANSI Code | Lamp Code | Beam | Volts | Avg. Rated Hours | Candle Power | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|--------|-----------------|-----------|-----------------|--------|-------|------------------|--------------|----------|--------|------------|-----------|
| 10 | MR8 | GZ4 | S4646 | n/a | 10MR8/NSP | SP9° | 12V | 2000 | tbd | C-6 | 1 1/4" | Box | 12 |
| 10 | MR8 | GZ4 | S4645 | n/a | 10MR8/NFL | NFL23° | 12V | 2000 | tbd | C-6 | 1 1/4" | Box | 12 |
| 5 | MR11 | GZ4 | S3194 | n/a | 5MR11/NSP | NSP9° | 12V | 2000 | tbd | C-6 | 1 1/4" | Box | 12 |
| 10 | MR11 | GZ4 | S3195 | n/a | 10MR11/SP | SP12° | 12V | 2000 | tbd | C-6 | 1 1/4" | Box | 12 |
| 20 | MR11 | GZ4 | S3150 | FTB | 20MR11/NSP | NSP9° | 12V | 2000 | 4100 | C-6 | 1 1/4" | Box | 12 |
| 20 | MR11 | GZ4 | S1990 | FIB/C/24 | 20MR11/NSP/C | NSP9° | 24V | 2000 | 4100 | C-6 | 1 1/4" | Box | 12 |
| 20 | MR11 | GZ4 | S3152 | FTC | 20MR11/SP | SP12° | 12V | 2000 | 1750 | C-6 | 1 1/4" | Box | 12 |
| 20 | MR11 | DC.Bay | S1954 | FST/C | 20MR11/DC/SP/C | SP12° | 12V | 2000 | 1750 | C-6 | 1 5/8" | Box | 12 |
| 20 | MR11 | GZ4 | S3154 | FTD | 20MR11/NFL | NFL24° | 12V | 2000 | 700 | C-6 | 1 1/4" | Box | 12 |
| 20 | MR11 | GZ4 | S1950 | FTD/C | 20MR11/NFL/C | NFL24° | 12V | 2000 | 700 | C-6 | 1 1/4" | Box | 12 |
| 20 | MR11 | GZ4 | S1988 | FTD/C/24 | 20MR11/NFL/C | NFL24° | 24V | 2000 | 700 | C-6 | 1 1/4" | Box | 12 |
| 20 | MR11 | DC.Bay | S1952 | FSV/C | 20MR11/DC/NFL/C | NFL24° | 12V | 2000 | 700 | C-6 | 1 5/8" | Box | 12 |
| 20 | MR11 | GZ4 | S4124 | n/a | 20MR11/FL/FR | FL36° | 12V | 2000 | 288 | C-6 | 1 1/4" | Box | 12 |
| 35 | MR11 | GZ4 | S3151 | FTE | 35MR11/NSP | NSP9° | 12V | 2000 | 7000 | C-6 | 1 1/4" | Box | 12 |
| 35 | MR11 | GZ4 | S1991 | FIE/C/24 | 35MR11/NSP/C | NSP9° | 24V | 2000 | tbd | C-6 | 1 1/4" | Box | 12 |
| 35 | MR11 | GZ4 | S3153 | FTF | 35MR11/SP | SP12° | 12V | 2000 | 1500 | C-6 | 1 1/4" | Box | 12 |
| 35 | MR11 | DC.Bay | S1955 | GDY/C | 35MR11/DC/SP/C | SP12° | 12V | 2000 | 1500 | C-6 | 1 5/8" | Box | 12 |
| 35 | MR11 | GZ4 | S3155 | FTH | 35MR11/NFL | NFL24° | 12V | 2000 | 700 | C-6 | 1 1/4" | Box | 12 |
| 35 | MR11 | GZ4 | S1951 | FTH/C | 35MR11/NFL/C | NFL24° | 12V | 2000 | 700 | C-6 | 1 1/4" | Box | 12 |
| 35 | MR11 | GZ4 | S1989 | FTH/C/24 | 35MR11/C | NFL24° | 24V | 2000 | 1500 | C-6 | 1 1/4" | Box | 12 |
| 35 | MR11 | DC.Bay | S1953 | GDZ/C | 35MR11/DC/NFL/C | NFL24° | 12V | 2000 | 700 | C-6 | 1 5/8" | Box | 12 |
| 35 | MR11 | GZ4 | S4125 | n/a | 35MR11/FL/FR | FL36° | 12V | 2000 | 520 | C-6 | 1 1/4" | Box | 12 |

halogen lamps

Halogen

MR16 Lamps 120V



2000 Hours

halogen lamps



JDR Lensed
120 Volt/Medium

S3139 50W Flood
S3113 75W Flood
S3114 100W Flood

120 Volt/Intermediate

S3115 75W Flood
S3116 100W Flood

Packing: Individually Boxed
12/ Carton



MR16 Lensed/Short
120 Volt/Med. Base

S4623 20W FL BAB/C
S4624 35W FL FMW/C
S4625 50W FL EXN/C

Packing: Individually Boxed
12/ Carton



MR16 Lensed Standard Pin
120 Volt/GX5.3 Base

S1976 20W FL BAB/C
S1977 35W FL FMW/C
S1978 50W FL EXN/C

Packing: Individually Boxed
12/ Carton



MR16 Lensed Wide Pin
120 Volt/G8 Base

S4626 20W FL BAB/C
S4627 35W FL FMW/C
S4618 50W FL EXN/C

Packing: Individually Boxed
12/ Carton



MR16 Lensed Twist Lock
120 Volt/GU10 Base

S3515 20W Flood
S3516 35W Flood
S3517 50W Flood

Packing: 12 Cards/Inner
120 Cards/Master



MR16 Lensed Twist Lock / Frosted
120 Volt/GU10 Base

S4127 20W Flood
S4128 35W Flood
S4129 50W Flood

Packing: Individually Boxed
12/ Carton

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Candle Power | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-------------------|--------|-------|------------------|--------------|----------|--------|------------|-----------------------|
| 20 | MR16 | GX5.3 | S1976 | 20MR16/FL/C | FL 36° | 120V | 2000 | 700 | CC-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | G8 | S4618 | 20MR16/G8/FL/C | FL 36° | 120V | 2000 | 700 | CC-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | GU10 | S3515 | 20MR16/GU10/FL | FL 36° | 120V | 2000 | 700 | CC-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | GU10 | S4127 | 20MR16/GU10/Frost | FL 36° | 120V | 2000 | 650 | CC-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | Med. | S4623 | 20MR16/S/FL/C | FL 36° | 120V | 2000 | 700 | CC-8 | 1 3/4" | Box | 12 |
| 35 | MR16 | GX5.3 | S1977 | 35MR16/FL/C | FL 36° | 120V | 2000 | 1250 | CC-8 | 1 7/8" | Box | 12 |
| 35 | MR16 | G8 | S4626 | 35MR16/G8/FL/C | FL 36° | 120V | 2000 | 1250 | CC-8 | 1 7/8" | Box | 12 |
| 35 | MR16 | GU10 | S3516 | 35MR16/GU10/FL | FL 36° | 120V | 2000 | 1250 | CC-8 | 1 7/8" | Box | 12 |
| 35 | MR16 | GU10 | S4128 | 35MR16/GU10/Frost | FL 36° | 120V | 2000 | 1200 | CC-8 | 1 7/8" | Box | 12 |
| 35 | MR16 | Med. | S4624 | 35MR16/S/FL/C | FL 36° | 120V | 2000 | 1250 | CC-8 | 1 3/4" | Box | 12 |
| 50 | MR16 | GX5.3 | S1978 | 50MR16/FL/C | FL 36° | 120V | 2000 | 1700 | CC-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | G8 | S4627 | 50MR16/G8/FL/C | FL 36° | 120V | 2000 | 1700 | CC-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | GU10 | S3517 | 50MR16/GU10/FL | FL 36° | 120V | 2000 | 1700 | CC-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | GU10 | S4129 | 50MR16/GU10/Frost | FL 36° | 120V | 2000 | 1650 | CC-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | Med. | S4625 | 50MR16/S/FL/C | FL 36° | 120V | 2000 | 1700 | CC-8 | 1 3/4" | Box | 12 |
| 50 | JDR | Med. | S3139 | 50JDR16/FL | FL 36° | 120V | 2000 | 1500 | CC-8 | 2 7/8" | Box | 12 |
| 75 | JDR | Int. | S3115 | 75JDR16/N/FL | FL 36° | 120V | 2000 | 1650 | CC-8 | 2 7/8" | Box | 12 |
| 75 | JDR | Med. | S3113 | 75JDR16/FL | FL 36° | 120V | 2000 | 1650 | CC-8 | 2 7/8" | Box | 12 |
| 100 | JDR | Int. | S3116 | 100JDR16/N/FL | FL 36° | 120V | 2000 | 1950 | CC-8 | 2 7/8" | Box | 12 |
| 100 | JDR | Med. | S3114 | 100JDR16/FL | FL 36° | 120V | 2000 | 1950 | CC-8 | 2 7/8" | Box | 12 |

2000 Hours / 12 Volt

MR16 Lamps



MR16 12 Volt

| | |
|--------------------------|-----------------------------|
| S1956 20W FL BAB | S1962 50W MFL EXZ |
| S1957 20W NSP ESX | S1963 50W VWFL FNV |
| S1958 35W NSP FRB | S1964 65W FL FPB |
| S1959 35W FL FMW | S1965 65W NSP FPA |
| S1960 50W FL EXN | Packing: Individually Boxed |
| S1961 50W NSP EXT | 12/Carton |

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | ANSI | Lamp Code | Beam | Volts | Avg. Rated Hours | Candle Power | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|-------|-----------------|------|------------|----------|-------|------------------|--------------|----------|--------|------------|-----------|
| 20 | MR16 | GX5.3 | S1957 | ESX | 20MR16/NSP | NSP 9° | 12V | 2000 | 4100 | C-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | GX5.3 | S1956 | BAB | 20MR16/FL | FL 36° | 12V | 2000 | 700 | C-6 | 1 7/8" | Box | 12 |
| 35 | MR16 | GX5.3 | S1958 | FRB | 35MR16/NSP | NSP 9° | 12V | 2000 | 7000 | C-6 | 1 7/8" | Box | 12 |
| 35 | MR16 | GX5.3 | S1959 | FMW | 35MR16/FL | FL 36° | 12V | 2000 | 1250 | C-6 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S1961 | EXT | 50MR16/NSP | NSP 9° | 12V | 2000 | 10000 | C-6 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S1962 | EXZ | 50MR16/NFL | NFL 18° | 12V | 2000 | 4400 | C-6 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S1960 | EXN | 50MR16/FL | FL 36° | 12V | 2000 | 1700 | C-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S1963 | FNV | 50MR16/WFL | VWFL 60° | 12V | 2000 | 2200 | C-6 | 1 7/8" | Box | 12 |
| 65 | MR16 | GX5.3 | S1965 | FPA | 65MR16/NSP | NSP 9° | 12V | 2000 | 9530 | C-6 | 1 7/8" | Box | 12 |
| 65 | MR16 | GX5.3 | S1964 | FPB | 65MR16 FPB | FL 36° | 12V | 2000 | 3600 | C-6 | 1 7/8" | Box | 12 |

Halogen MR16 Lamps



2000 Hours / 12 & 24 Volt

MR16 Bayonet / Lensed 12 Volt

- S1970 20W FL GES/C
- S1971 20W NSP GEV/C
- S1972 50W FL GBW/C
- S1973 50W NSP GBT/C
- S1974 65W FL FPB/C
- S1975 65W NSP FPA/C

Packing: Individually Boxed
12/Carton



MR16 Lensed 24 Volt

- S1992 20W FL
- S1993 35W FL
- S1994 50W FL
- S1995 20W SP
- S1996 35W SP
- S1997 50W SP

Packing: Individually Boxed
12/Carton



MR16 Lensed 12 Volt

- S1966 20W FL BAB/C
- S1967 20W NSP ESX/C
- S4365 35W FL FMW/C
- S4364 35W NSP FRB/C
- S3169 50W FL EXN/C
- S3170 50W NSP EXT/C
- S1968 65W FL FPB/C
- S1969 65W NSP FPA/C

Packing: Individually Boxed
20/Carton



MR16 Frosted Lensed 12 Volt

- S4120 20W FL BAB/C
- S4121 35W FL FMW/C
- S4122 50W FL EXN/C
- S4123 65W FL FPB/C

Packing: Individually Boxed,
12/Carton



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Candle Power | Filament | M.O.L. | Pack. Type | Mst.Ctn./Inner Pack |
|-------|-----------|----------|-----------------|-------------------|--------|-------|------------------|--------------|----------|--------|------------|---------------------|
| 20 | MR16 | GX5.3 | S1966 | 20MR16/FL/C | FL 36° | 12V | 2000 | 700 | C-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | GX5.3 | S4120 | 20MR16/FL/FROST/C | FL 36° | 12V | 2000 | 288 | C-6 | 1 7/8" | Box | 12 |
| 20 | MR16 | D.C.Bay. | S1970 | 20MR16/FL/DC/C | FL 36° | 12V | 2000 | 700 | C-6 | 1 7/8" | Box | 12 |
| 20 | MR16 | GX5.3 | S1992 | 20MR16/FL/C | FL 36° | 24V | 2000 | 700 | C-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | GX5.3 | S1967 | 20MR16/NSP/C | NSP 9° | 12V | 2000 | 4100 | C-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | D.C.Bay. | S1971 | 20MR16/NSP/DC/C | NSP 9° | 12V | 2000 | 4100 | C-8 | 1 7/8" | Box | 12 |
| 20 | MR16 | GX5.3 | S1995 | 20MR16/NSP/C | NSP 9° | 24V | 2000 | 4100 | C-8 | 1 7/8" | Box | 12 |
| 35 | MR16 | GX5.3 | S4365 | 35MR16/FL/C | FL 36° | 12V | 2000 | 1250 | C-8 | 1 7/8" | Box | 12 |
| 35 | MR16 | GX5.3 | S1993 | 35MR16/FL/C | FL 36° | 24V | 2000 | 700 | C-8 | 1 7/8" | Box | 12 |
| 35 | MR16 | GX5.3 | S4121 | 35MR16/FL/FROST | FL 36° | 12V | 2000 | 520 | C-6 | 1 7/8" | Box | 12 |
| 35 | MR16 | GX5.3 | S4364 | 35MR16/NSP/C | NSP 9° | 12V | 2000 | 7000 | C-8 | 1 7/8" | Box | 12 |
| 35 | MR16 | GX5.3 | S1996 | 35MR16/NSP/C | NSP 9° | 24V | 2000 | 7000 | C-6 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S3169 | 50MR16/FL/C | FL 36° | 12V | 2000 | 1700 | C-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S4122 | 50MR16/FL/FROST | FL 36° | 12V | 2000 | 820 | C-6 | 1 7/8" | Box | 12 |
| 50 | MR16 | D.C.Bay. | S1972 | 50MR16/FL/DC/C | FL 36° | 12V | 2000 | 1700 | C-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S1994 | 50MR16/FL | FL 36° | 24V | 2000 | 1700 | C-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S3170 | 50MR16/NSP/C | NSP 9° | 12V | 2000 | 10000 | C-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | D.C.Bay. | S1973 | 50MR16/NSP/DC/C | NSP 9° | 12V | 2000 | 10000 | C-8 | 1 7/8" | Box | 12 |
| 50 | MR16 | GX5.3 | S1997 | 50MR16/NSP/C | NSP 9° | 24V | 2000 | 10000 | C-8 | 1 7/8" | Box | 12 |
| 65 | MR16 | GX5.3 | S1968 | 65MR16/FL/C | FL 36° | 12V | 2000 | 3600 | C-8 | 1 7/8" | Box | 12 |
| 65 | MR16 | GX5.3 | S4123 | 65MR16/FL/FROST/C | FL 36° | 12V | 2000 | 880 | C-6 | 1 7/8" | Box | 12 |
| 65 | MR16 | D.C.Bay. | S1974 | 65MR16/FL/DC/C | FL 36° | 12V | 2000 | tbd | C-6 | 1 7/8" | Box | 12 |
| 65 | MR16 | GX5.3 | S1969 | 65MR16/NSP/C | NSP 9° | 12V | 2000 | 9500 | C-8 | 1 7/8" | Box | 12 |
| 65 | MR16 | D.C.Bay. | S1975 | 65MR16/NSP/DC/C | NSP 9° | 12V | 2000 | 9500 | C-8 | 1 7/8" | Box | 12 |

halogen lamps

Halogen

4000 Hours

Not Shown Actual Size

MR16 Specialty Lamps



Alluminized Reflector

- Projects Heat & Light out the front of the lamp
- Minimizes the "Backlight Effect"
- Constant Color Technology



Hard Coated
Dichroic Reflector

- Projects Heat out the back of the lamp
- Constant Color Technology



Energy Saving

- Hard Coated Dichroic Reflector
- Infra-Red Reflective Coating
- Constant Color Technology
- Lensed

| Watts | Bulb Type | Base | Satco Order No. | ANSI | Lamp Code | Volts | Avg. Rated Hours | Candle Power | Filament | M.O.L. | Pack. Type | Mst. Ctn |
|--|-----------|-------|-----------------|-------|-------------------|-------|------------------|--------------|----------|--------|------------|----------|
| Aluminized Reflector | | | | | | | | | | | | |
| 20 | MR16 | GU5.3 | S2601 | BAB | 20MR16/B/FL35 | 12V | 4000 | 625 | AX | 1 3/4" | Box | 10 |
| 20 | MR16 | GU5.3 | S2602 | BAB/C | 20MR16/B/FL35/C | 12V | 4000 | 600 | AX | 1 3/4" | Box | 10 |
| 20 | MR16 | GU5.3 | S2603 | ESX | 20MR16/B/NSP8 | 12V | 4000 | 4650 | AX | 1 3/4" | Box | 10 |
| 20 | MR16 | GU5.3 | S2604 | ESX/C | 20MR16/B/NSP8/C | 12V | 4000 | 4400 | AX | 1 3/4" | Box | 10 |
| 35 | MR16 | GU5.3 | S2605 | FMW | 35MR16/B/FL35 | 12V | 4000 | 1300 | AX | 1 3/4" | Box | 10 |
| 35 | MR16 | GU5.3 | S2606 | FRB | 35MR16/B/NSP10 | 12V | 4000 | 8700 | AX | 1 3/4" | Box | 10 |
| 50 | MR16 | GU5.3 | S2607 | EXN | 50MR16/B/FL35 | 12V | 4000 | 1900 | AX | 1 3/4" | Box | 10 |
| 50 | MR16 | GU5.3 | S2608 | EXN/C | 50MR16/B/FL35/C | 12V | 4000 | 1800 | AX | 1 3/4" | Box | 10 |
| 50 | MR16 | GU5.3 | S2609 | EXZ | 50MR16/B/NFL25 | 12V | 4000 | 3000 | AX | 1 3/4" | Box | 10 |
| 50 | MR16 | GU5.3 | S2610 | EXT | 50MR16/B/NSP11 | 12V | 4000 | 10500 | AX | 1 3/4" | Box | 10 |
| 50 | MR16 | GU5.3 | S2611 | EXT/C | 50MR16/B/NSP11/C | 12V | 4000 | 10000 | AX | 1 3/4" | Box | 10 |
| 65 | MR16 | GU5.3 | S2612 | FPB | 65MR16/B/FL40 | 12V | 4000 | 2100 | AX | 1 3/4" | Box | 10 |
| 65 | MR16 | GU5.3 | S2613 | FPC | 65MR16/B/NFL25 | 12V | 4000 | 3600 | AX | 1 3/4" | Box | 10 |
| 65 | MR16 | GU5.3 | S2614 | FPA | 65MR16/B/NSP10 | 12V | 4000 | 12500 | AX | 1 3/4" | Box | 10 |
| Hard Coated Dichroic Reflector | | | | | | | | | | | | |
| 20 | MR16 | GU5.3 | S2615 | BAB | 20MR16/T/FL40 | 12V | 4000 | 700 | AX | 1 3/4" | Box | 20 |
| 20 | MR16 | GU5.3 | S2616 | ESX | 20MR16/T/NSP10 | 12V | 4000 | 5000 | AX | 1 3/4" | Box | 20 |
| 20 | MR16 | GU5.3 | S2617 | n/a | 20MR16/T/WFL60 | 12V | 4000 | 350 | AX | 1 3/4" | Box | 20 |
| 35 | MR16 | GU5.3 | S2618 | FMW | 35MR16/T/FL40 | 12V | 4000 | 1250 | AX | 1 3/4" | Box | 20 |
| 35 | MR16 | GU5.3 | S2619 | n/a | 35MR16/T/NFL25 | 12V | 4000 | 3100 | AX | 1 3/4" | Box | 20 |
| 35 | MR16 | GU5.3 | S2620 | FRB | 35MR16/T/NSP10 | 12V | 4000 | 8300 | AX | 1 3/4" | Box | 20 |
| 35 | MR16 | GU5.3 | S2621 | n/a | 35MR16/T/WFL60 | 12V | 4000 | 650 | AX | 1 3/4" | Box | 20 |
| 50 | MR16 | GU5.3 | S2622 | EXN | 50MR16/T/FL40 | 12V | 4000 | 2000 | AX | 1 3/4" | Box | 20 |
| 50 | MR16 | GU5.3 | S2623 | EXZ | 50MR16/T/NFL25 | 12V | 4000 | 3200 | AX | 1 3/4" | Box | 20 |
| 50 | MR16 | GU5.3 | S2624 | EXT | 50MR16/T/NSP10 | 12V | 4000 | 11500 | AX | 1 3/4" | Box | 20 |
| 50 | MR16 | GU5.3 | S2625 | FNV | 50MR16/T/WFL60 | 12V | 4000 | 1000 | AX | 1 3/4" | Box | 20 |
| 65 | MR16 | GU5.3 | S2626 | FPB | 65MR16/T/FL40 | 12V | 4000 | 2100 | AX | 1 3/4" | Box | 20 |
| 65 | MR16 | GU5.3 | S2627 | FPC | 65MR16/T/NFL25 | 12V | 4000 | 4000 | AX | 1 3/4" | Box | 20 |
| 65 | MR16 | GU5.3 | S2628 | FPA | 65MR16/T/NSP10 | 12V | 4000 | 14000 | AX | 1 3/4" | Box | 20 |
| 65 | MR16 | GU5.3 | S2629 | n/a | 65MR16/T/WFL60 | 12V | 4000 | 1050 | AX | 1 3/4" | Box | 20 |
| Infra-Red Reflecting Energy Saver | | | | | | | | | | | | |
| 20 | MR16 | GU5.3 | S2630 | n/a | 20MR16/IR/FL40/C | 12V | 4000 | 1000 | AX | 1 3/4" | Box | 20 |
| 20 | MR16 | GU5.3 | S2631 | n/a | 20MR16/IR/NFL25/C | 12V | 4000 | 2300 | AX | 1 3/4" | Box | 20 |
| 20 | MR16 | GU5.3 | S2632 | n/a | 20MR16/IR/NSP10/C | 12V | 4000 | 6000 | AX | 1 3/4" | Box | 20 |
| 20 | MR16 | GU5.3 | S2633 | n/a | 20MR16/IR/WFL60/C | 12V | 4000 | 450 | AX | 1 3/4" | Box | 20 |
| 37 | MR16 | GU5.3 | S2634 | n/a | 37MR16/IR/FL40/C | 12V | 4000 | 2200 | AX | 1 3/4" | Box | 20 |
| 37 | MR16 | GU5.3 | S2635 | n/a | 37MR16/IR/NFL25/C | 12V | 4000 | 4400 | AX | 1 3/4" | Box | 20 |
| 37 | MR16 | GU5.3 | S2636 | n/a | 37MR16/IR/NSP10/C | 12V | 4000 | 12500 | AX | 1 3/4" | Box | 20 |
| 37 | MR16 | GU5.3 | S2637 | n/a | 37MR16/IR/WFL60/C | 12V | 4000 | 1100 | AX | 1 3/4" | Box | 20 |
| 50 | MR16 | GU5.3 | S2638 | n/a | 50MR16/IR/FL40/C | 12V | 4000 | 2850 | AX | 1 3/4" | Box | 20 |
| 50 | MR16 | GU5.3 | S2639 | n/a | 50MR16/IR/NFL25/C | 12V | 4000 | 5700 | AX | 1 3/4" | Box | 20 |
| 50 | MR16 | GU5.3 | S2640 | n/a | 50MR16/IR/NSP10/C | 12V | 4000 | 15000 | AX | 1 3/4" | Box | 20 |
| 50 | MR16 | GU5.3 | S2641 | n/a | 50MR16/IR/WFL60/C | 12V | 4000 | 1430 | AX | 1 3/4" | Box | 20 |

halogen lamps

Closed Aluminum

Reflector (ALR) Lamps

2000 Hours/12 Volt

halogen lamps



37mm ALR
D.C. Bayonet

12 Volt

S2642 20W Narrow Spot GBD

Packing: Individually Boxed
Master/50, Inner/5



37mm ALR
D.C. Bayonet

12 Volt

S2643 20W Spot GBE

S2644 20W Flood GBF

Packing: Individually Boxed
Master/50, Inner/5



56mm ALR
D.C. Bayonet

12 Volt

S2645 50W Flood GBK

Packing: Individually Boxed
Master/50, Inner/5



56mm ALR
D.C. Bayonet

12 Volt

S2646 50W Spot GBJ

Packing: Individually Boxed
Master/50, Inner/5

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Candle Power | Kelvin | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|----------|-----------------|-------------------|------|-------|------------------|--------------|--------|--------|------------|-----------------------|
| 20 | 37mm ALR | D.C. Bay | S2642 | 20ALR12/NSP6-GBD | 6° | 12V | 2000 | 6400 | 3000K | 1 3/8" | Box | 50/5 |
| 20 | 37mm ALR | D.C. Bay | S2643 | 20ALR12/SP18-GBE | 18° | 12V | 2000 | 1000 | 3000K | 1 3/8" | Box | 50/5 |
| 20 | 37mm ALR | D.C. Bay | S2644 | 20ALR12/FL34-GBF | 34° | 12V | 2000 | 350 | 3000K | 1 3/8" | Box | 50/5 |
| 50 | 56mm ALR | D.C. Bay | S2646 | 50ALR18/SP10-GBJ | 10° | 12V | 2000 | 12,000 | 3000K | 2 1/2" | Box | 50/5 |
| 50 | 56mm ALR | D.C. Bay | S2645 | 50ALR18/NFL22-GBK | 22° | 12V | 2000 | 2000 | 3000K | 2 1/2" | Box | 50/5 |

Halogen Aluminum Reflectors **AR70 & AR111**

3000 Hours

UV stop capsule with axial filament in precisely engineered aluminum reflector.



AR111



AR70

Screw Terminal Base

| | |
|---------------------------------|----------------------------------|
| S4685 35 Watt Super Spot | S4692 75 Watt Flood |
| S4686 35 Watt Spot | S4693 75 Watt Wide Flood |
| S4687 35 Watt Flood | S4694 100 Watt Spot |
| S4688 50 Watt Super Spot | S4695 100 Watt Flood |
| S4689 50 Watt Spot | S4696 100 Watt Wide Flood |
| S4690 50 Watt Flood | Packing: Individually Boxed |
| S4691 75 Watt Spot | 6/Master |

D.C. Bayonet Base

| |
|-----------------------------|
| S4680 20 Watt Spot |
| S4681 20 Watt Flood |
| S4682 50 Watt Spot |
| S4683 50 Watt Flood |
| Packing: Individually Boxed |
| 10/Master |

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP* | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------------|-----------------|----------------|----------------|-------|------------------|-------|----------|----------|------------|-----------|
| 20 | AR70 | DC Bayonet | S4680 | 20AR70/SP8 | Spot 8° | 12V | 3000 | 7700 | C-8 | 1 15/16" | Box | 10 |
| 20 | AR70 | DC Bayonet | S4681 | 20AR70/FL25 | Flood 25° | 12V | 3000 | 900 | C-8 | 1 15/16" | Box | 10 |
| 50 | AR70 | DC Bayonet | S4682 | 50AR70/SP8 | Spot 8° | 12V | 3000 | 12500 | C-8 | 1 15/16" | Box | 10 |
| 50 | AR70 | DC Bayonet | S4683 | 50AR70/FL25 | Flood 25° | 12V | 3000 | 2600 | C-8 | 1 15/16" | Box | 10 |
| 35 | AR111 | G53 | S4684 | 35AR111/SSP4 | Super Spot 4° | 12V | 3000 | 40000 | C-8 | 2 3/8" | Box | 6 |
| 35 | AR111 | G53 | S4686 | 35AR111/SP8 | Spot 8° | 12V | 3000 | 14000 | C-8 | 2 5/16" | Box | 6 |
| 35 | AR111 | G53 | S4687 | 35AR111/FL25 | Flood 25° | 12V | 3000 | 2500 | C-8 | 2 5/16" | Box | 6 |
| 50 | AR111 | G53 | S4688 | 50AR111/SSP4 | Super Spot 4° | 12V | 3000 | 45000 | C-8 | 2 3/8" | Box | 6 |
| 50 | AR111 | G53 | S4689 | 50AR111/SP8 | Spot 8° | 12V | 3000 | 20000 | C-8 | 2 1/4" | Box | 6 |
| 50 | AR111 | G53 | S4690 | 50AR111/FL25 | Flood 25° | 12V | 3000 | 4000 | C-8 | 2 5/16" | Box | 6 |
| 75 | AR111 | G53 | S4691 | 75AR111/SP8 | Spot 8° | 12V | 3000 | 30000 | C-8 | 2 1/4" | Box | 6 |
| 75 | AR111 | G53 | S4692 | 75AR111/FL25 | Flood 25° | 12V | 3000 | 5300 | C-8 | 2 5/16" | Box | 6 |
| 75 | AR111 | G53 | S4693 | 75AR111/WFL45 | Wide Flood 45° | 12V | 3000 | 2000 | C-8 | 2 3/8" | Box | 6 |
| 100 | AR111 | G53 | S4694 | 100AR111/SP8 | Spot 8° | 12V | 3000 | 48000 | C-8 | 2 1/4" | Box | 6 |
| 100 | AR111 | G53 | S4695 | 100AR111/FL25 | Flood 25° | 12V | 3000 | 8500 | C-8 | 2 5/16" | Box | 6 |
| 100 | AR111 | G53 | S4696 | 100AR111/WFL45 | Wide Flood 45° | 12V | 3000 | 2800 | C-8 | 2 3/8" | Box | 6 |

halogen lamps



Halogen Sealed Beam Reflectors **PAR36/PAR56/PAR64**

halogen lamps



PAR36
Screw Terminal

PAR56
Mogul End Prong

PAR64
Mogul End Prong

2 Piece Construction
12 Volt

2 Piece Construction
120 Volt

2 Piece Construction
120 Volt

- S4807** 36 Watt Very Narrow Spot
 - S4808** 36 Watt Narrow Spot
 - S4809** 36 Watt Wide Flood
 - S4806** 50 Watt Narrow Spot
- Packing: Individually Boxed
12/Master

- S4669** 500 Watt Med. Flood
 - S4668** 500 Watt Narrow Spot
 - S4670** 500 Watt Wide Flood
- Packing: Individually Boxed
12/Master

- S4672** 1000 Watt Med. Flood
 - S4671** 1000 Watt Narrow Spot
 - S4673** 1000 Watt Wide Flood
- Packing: Individually Boxed
6/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP* | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|-----------------|-----------------|------------------|-----------------|-------|------------------|--------|--------|----------|--------|------------|-----------|
| 36 | PAR36 | Screw Term. | S4807 | 36PAR36/CAP/VNSP | Spot 5° | 12V | 4000 | 17000 | 500 | C-8 | 2 3/4" | Box | 12 |
| 36 | PAR36 | Screw Term. | S4808 | 36PAR36/CAP/NSP | Spot 13° | 12V | 4000 | 3500 | 500 | C-8 | 2 3/4" | Box | 12 |
| 36 | PAR36 | Screw Term. | S4809 | 36PAR36/CAP/WFL | Flood 32° | 12V | 4000 | 1000 | 500 | C-8 | 2 3/4" | Box | 12 |
| 50 | PAR36 | Screw Term. | S4806 | 50PAR36/CAP/NSP6 | Spot 6° | 12V | 4000 | 25000 | 700 | C-8 | 2 3/4" | Box | 12 |
| 500 | PAR56 | Mogul End Prong | S4668 | 500PAR56Q/NSP | Narrow Spot 15° | 120V | 4000 | 78500 | 8800 | CC-6 | 5" | Box | 12 |
| 500 | PAR56 | Mogul End Prong | S4669 | 500PAR56Q/MFL | Med. Flood 30° | 120V | 4000 | 40000 | 8800 | CC-6 | 5" | Box | 12 |
| 500 | PAR56 | Mogul End Prong | S4670 | 500PAR56Q/WFL | Wide Flood 45° | 120V | 4000 | 19500 | 8800 | CC-6 | 5" | Box | 12 |
| 1000 | PAR64 | Mogul End Prong | S4671 | 1000PAR64Q/NSP | Narrow Spot 20° | 120V | 4000 | 135000 | 19400 | CC-6 | 6" | Box | 6 |
| 1000 | PAR64 | Mogul End Prong | S4672 | 1000PAR64Q/MFL | Med. Flood 30° | 120V | 4000 | 82000 | 19400 | CC-6 | 6" | Box | 6 |
| 1000 | PAR64 | Mogul End Prong | S4673 | 1000PAR64Q/WFL | Wide Flood 60° | 120V | 4000 | 23000 | 19400 | CC-6 | 6" | Box | 6 |

Halogen General Service Lamps



**BRILLIANT
WHITE LIGHT**
4000 Hours
**EXTRA
LONG LIFE!**



Dual
halogen
capsules
create
3 light levels

**3 Way
Reading Light
Soft White**

Medium Base/120 Volt

S4505 30/70/100 Watt
S4506 50/100/150 Watt

Packing: 1/Sleeve
12/Inner
36/Master



A-Type

Medium Base/120 Volt

S4600 60 Watt White
S4601 75 Watt White
S4602 100 Watt White
S4603 60 Watt Clear
S4604 150 Watt White

Packing: 6/Inner
6/Inner - Tray Pack
60/Master

Not Shown Actual Size



**Double-Envelope
JDD Type**

Medium Base/120 Volt

S3472 75 Watt Clear
S3476 75 Watt Frosted
S3473 100 Watt Clear
S3477 100 Watt Frosted
S3474 150 Watt Clear
S3478 150 Watt Frosted
S3475 250 Watt Clear
S3479 250 Watt Frosted

Packing: 1 Bulb/Card
12 Cards/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 60 | BT15 | Med. | S4603 | 60BT15/CL | Clear | 120V | 5000 | 700 | CC-8 | 4" | Card/1 | 60/6 |
| 60 | BT15 | Med. | S4600 | 60BT15/W | White | 120V | 5000 | 600 | CC-8 | 4" | Card/1 | 60/6 |
| 75 | BT15 | Med. | S4601 | 75BT15/W | White | 120V | 5000 | 800 | CC-8 | 4" | Card/1 | 60/6 |
| 75 | T10 | Med. | S3472 | 75T10Q/CL | Clear | 120V | 2000 | 1050 | CC-8 | 4" | Card/1 | 12 |
| 75 | T10 | Med. | S3476 | 75T10Q/F | Frosted | 120V | 2000 | 1000 | CC-8 | 4" | Card/1 | 12 |
| 100 | BT15 | Med. | S4602 | 100BT15/W | White | 120V | 5000 | 1200 | CC-8 | 4" | Card/1 | 60/6 |
| 100 | T10 | Med. | S3473 | 100T10Q/CL | Clear | 120V | 2000 | 1500 | CC-8 | 4" | Card/1 | 12 |
| 100 | T10 | Med. | S3477 | 100T10Q/F | Frosted | 120V | 2000 | 1420 | CC-8 | 4" | Card/1 | 12 |
| 150 | BT15 | Med. | S4604 | 150BT15/W | White | 120V | 5000 | 1600 | CC-8 | 4" | Card/1 | 60/6 |
| 150 | T10 | Med. | S3474 | 150T10Q/CL | Clear | 120V | 2000 | 2500 | CC-8 | 4" | Card/1 | 12 |
| 150 | T10 | Med. | S3478 | 150T10Q/F | Frosted | 120V | 2000 | 2300 | CC-8 | 4" | Card/1 | 12 |
| 250 | T10 | Med. | S3475 | 250T10Q/CL | Clear | 120V | 2000 | 4200 | CC-8 | 4" | Card/1 | 12 |
| 250 | T10 | Med. | S3479 | 250T10Q/F | Frosted | 120V | 2000 | 3900 | CC-8 | 4" | Card/1 | 12 |

3-Way Reading Light

| | | | | | | | | | | | | |
|-----|-----|----------|--------------|-----------------|-------|------|------|------|------|---------|--------|-------|
| 30 | | | | | | | | 295 | CC-8 | | | |
| 70 | A21 | E26/Med. | S4505 | 30/70/100A21/W | White | 120V | 4000 | 785 | CC-8 | 5 1/16" | Sleeve | 36/12 |
| 100 | | | | | | | | 1080 | | | | |
| 50 | | | | | | | | 585 | CC-8 | | | |
| 100 | A21 | E26/Med. | S4506 | 50/100/150A21/W | White | 120V | 4000 | 1400 | CC-8 | 5 1/16" | Sleeve | 36/12 |
| 150 | | | | | | | | 1985 | | | | |

halogen lamps



Halogen



JD Bayonet Lamps

2000 Hours

halogen lamps

JD Bayonet

120 Volt

- S1979** 35 Watt
- S1981** 50 Watt
- S3159** 75 Watt
- S3147** 100 Watt
- S3122** 150 Watt
- S3123** 250 Watt
- S1983** 500 Watt

Packing:
Individually Boxed
12/Carton



JD Frosted Bayonet

120 Volt

- S1980** 35 Watt
- S1982** 50 Watt
- S1919** 75 Watt
- S1920** 100 Watt
- S1921** 150 Watt
- S1922** 250 Watt
- S1984** 500 Watt

Packing:
Individually Boxed
12/Carton



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|---------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------|
| 35 | T4 | DC. Bay | S1979 | 35Q/CL | Clear | 120V | 2000 | 400 | CC-8 | 2 23/32" | Box | 12 |
| 35 | T4 | DC. Bay | S1980 | 35Q/F | Frost | 120V | 2000 | 360 | CC-8 | 2 23/32" | Box | 12 |
| 50 | T4 | DC. Bay | S1981 | 50Q/CL | Clear | 120V | 2000 | 750 | CC-8 | 2 23/32" | Box | 12 |
| 50 | T4 | DC. Bay | S1982 | 50Q/F | Frost | 120V | 2000 | 675 | CC-8 | 2 23/32" | Box | 12 |
| 75 | T4 | DC. Bay | S3159 | 75Q/CL | Clear | 120V | 2000 | 1250 | CC-8 | 2 13/32" | Box | 12 |
| 75 | T4 | DC. Bay | S1919 | 75Q/F | Frost | 120V | 2000 | 1125 | CC-8 | 2 13/32" | Box | 12 |
| 100 | T4 | DC. Bay | S3147 | 100Q/CL | Clear | 120V | 2000 | 1600 | CC-8 | 2 13/32" | Box | 12 |
| 100 | T4 | DC. Bay | S1920 | 100Q/F | Frost | 120V | 2000 | 1440 | CC-8 | 2 13/32" | Box | 12 |
| 150 | T4.5 | DC. Bay | S3122 | 150Q/CL | Clear | 120V | 2000 | 2400 | CC-8 | 2 13/32" | Box | 12 |
| 150 | T4.5 | DC. Bay | S1921 | 150Q/F | Frost | 120V | 2000 | 2160 | CC-8 | 2 13/32" | Box | 12 |
| 250 | T4.5 | DC. Bay | S3123 | 250Q/CL | Clear | 120V | 2000 | 4350 | CC-8 | 2 27/32" | Box | 12 |
| 250 | T4.5 | DC. Bay | S1922 | 250Q/F | Frost | 120V | 2000 | 3915 | CC-8 | 2 27/32" | Box | 12 |
| 500 | T4.5 | DC. Bay | S1983 | 500Q/CL | Clear | 120V | 2000 | 8500 | CC-8 | 3 3/4" | Box | 12 |
| 500 | T4.5 | DC. Bay | S1984 | 500Q/F | Frost | 120V | 2000 | 7650 | CC-8 | 3 3/4" | Box | 12 |

2000 Hours



JD

Clear Mini Can

120 Volt

- S3165** 35 Watt
- S3162** 50 Watt
- S3157** 75 Watt
- S3107** 100 Watt
- S3108** 150 Watt
- S3109** 250 Watt
- S3181** 500 Watt

130 Volt

- S3198** 50 Watt

Packing: Individually Boxed
12/ Carton



JD

Frosted Mini Can

120 Volt

- S1913** 35 Watt
- S1914** 50 Watt
- S1915** 75 Watt
- S1916** 100 Watt
- S1917** 150 Watt
- S1918** 250 Watt
- S3182** 500 Watt

Packing:

Individually Boxed
12/ Carton



JD E-14

European

120 Volt

- S3132** 100 Watt
- S3133** 150 Watt
- S3134** 250 Watt

Packing:
Individually Boxed
12/ Carton

**Not Shown
Actual Size**

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------|
| 35 | T4 | E11 | S3165 | 35Q/CL | Clear | 120V | 2000 | 400 | CC-8 | 2 5/16" | Box | 12 |
| 35 | T4 | E11 | S1913 | 35Q/F | Frost | 120V | 2000 | 360 | CC-8 | 2 5/16" | Box | 12 |
| 50 | T4 | E11 | S3162 | 50Q/CL | Clear | 120V | 2000 | 750 | CC-8 | 2 5/16" | Box | 12 |
| 50 | T4 | E11 | S1914 | 50Q/F | Frost | 120V | 2000 | 675 | CC-8 | 2 5/16" | Box | 12 |
| 50 | T4 | E11 | S3198 | 50Q/CL | Clear | 130V | 2000 | 750 | CC-8 | 2 5/16" | Box | 12 |
| 75 | T4 | E11 | S3157 | 75Q/CL | Clear | 120V | 2000 | 1250 | CC-8 | 2 11/16" | Box | 12 |
| 75 | T4 | E11 | S1915 | 75Q/F | Frost | 120V | 2000 | 1125 | CC-8 | 2 11/16" | Box | 12 |
| 100 | T4 | E11 | S3107 | 100Q/CL | Clear | 120V | 2000 | 1600 | CC-8 | 2 11/16" | Box | 12 |
| 100 | T4 | E11 | S1916 | 100Q/F | Frost | 120V | 2000 | 1440 | CC-8 | 2 11/16" | Box | 12 |
| 100 | T4.5 | E14 | S3132 | 100Q/CL | Clear | 120V | 2000 | 1600 | CC-8 | 2 15/16" | Box | 12 |
| 150 | T4.5 | E11 | S3108 | 150Q/CL | Clear | 120V | 2000 | 2400 | CC-8 | 2 23/32" | Box | 12 |
| 150 | T4.5 | E11 | S1917 | 150Q/F | Frost | 120V | 2000 | 2160 | CC-8 | 2 23/32" | Box | 12 |
| 150 | T4.5 | E14 | S3133 | 150Q/CL | Clear | 120V | 2000 | 2400 | CC-8 | 3 1/32" | Box | 12 |
| 250 | T4.5 | E11 | S3109 | 250Q/CL | Clear | 120V | 2000 | 4350 | CC-8 | 3 5/32" | Box | 12 |
| 250 | T4.5 | E11 | S1918 | 250Q/F | Frost | 120V | 2000 | 3915 | CC-8 | 3 5/32" | Box | 12 |
| 250 | T4.5 | E14 | S3134 | 250Q/CL | Clear | 120V | 2000 | 4350 | CC-8 | 3 11/32" | Box | 12 |
| 500 | T4.5 | E11 | S3181 | 500Q/CL | Clear | 120V | 2000 | 8500 | CC-8 | 3 15/32" | Box | 12 |
| 500 | T4.5 | E11 | S3182 | 500Q/F | Frost | 120V | 2000 | 7650 | CC-8 | 3 15/32" | Box | 12 |

Krypton/Xenon

High Performance Lamps

3000 Hours
120 Volt



Frosted
E-11
Mini Can Base
S4489 20 Watt
S4490 40 Watt
S4491 60 Watt



Frosted
D.C.
Bayonet Base
S4495 20 Watt
S4496 40 Watt
S4497 60 Watt



Clear
D.C.
Bayonet Base
S4492 20 Watt
S4493 40 Watt
S4494 60 Watt



Clear
E-11
Mini Can Base
S4486 20 Watt
S4487 40 Watt
S4488 60 Watt



Frosted
E-12
Candelabra Base
S4483 20 Watt
S4484 40 Watt
S4485 60 Watt



Clear
E-12
Candelabra Base
S4480 20 Watt
S4481 40 Watt
S4482 60 Watt

White light similar to halogen • Less heat • Lamps can be touched
Fully dimmable • No Significant UV.

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|----------|-----------------|------------|--------|-------|------------------|--------|----------|---------|------------|----------------------|
| 20 | T3 | E12 | S4480 | KX20CL/E12 | Clear | 120V | 3000 | 200 | CC-8 | 2 7/16" | Box | 100/10 |
| 20 | T3 | E12 | S4483 | KX20FR/E12 | Frost. | 120V | 3000 | 200 | CC-8 | 2 7/16" | Box | 100/10 |
| 20 | T3 | E11 | S4486 | KX20CL/E11 | Clear | 120V | 3000 | 200 | CC-8 | 2 5/16" | Box | 100/10 |
| 20 | T3 | E11 | S4489 | KX20FR/E11 | Frost | 120V | 3000 | 200 | CC-8 | 2 5/16" | Box | 100/10 |
| 20 | T3 | D.C. Bay | S4492 | KX20CL/DC | Clear | 120V | 3000 | 200 | CC-8 | 2 1/4" | Box | 100/10 |
| 20 | T3 | D.C. Bay | S4495 | KX20FR/DC | Frost | 120V | 3000 | 200 | CC-8 | 2 1/4" | Box | 100/10 |
| 40 | T3 | E12 | S4481 | KX40CL/E12 | Clear | 120V | 3000 | 560 | CC-8 | 2 7/16" | Box | 100/10 |
| 40 | T3 | E12 | S4484 | KX40FR/E12 | Frost | 120V | 3000 | 560 | CC-8 | 2 7/16" | Box | 100/10 |
| 40 | T3 | E11 | S4487 | KX40CL/E11 | Clear | 120V | 3000 | 560 | CC-8 | 2 5/16" | Box | 100/10 |
| 40 | T3 | E11 | S4490 | KX40FR/E11 | Frost | 120V | 3000 | 560 | CC-8 | 2 5/16" | Box | 100/10 |
| 40 | T3 | D.C. Bay | S4493 | KX40CL/DC | Clear | 120V | 3000 | 560 | CC-8 | 2 1/4" | Box | 100/10 |
| 40 | T3 | D.C. Bay | S4496 | KX40FR/DC | Frost | 120V | 3000 | 560 | CC-8 | 2 1/4" | Box | 100/10 |
| 60 | T3 | E12 | S4482 | KX60CL/E12 | Clear | 120V | 3000 | 960 | CC-8 | 2 7/16" | Box | 100/10 |
| 60 | T3 | E12 | S4485 | KX60FR/E12 | Frost | 120V | 3000 | 960 | CC-8 | 2 7/16" | Box | 100/10 |
| 60 | T3 | E11 | S4488 | KX60CL/E11 | Clear | 120V | 3000 | 960 | CC-8 | 2 5/16" | Box | 100/10 |
| 60 | T3 | E11 | S4491 | KX60FR/E11 | Frost | 120V | 3000 | 960 | CC-8 | 2 5/16" | Box | 100/10 |
| 60 | T3 | D.C. Bay | S4494 | KX60CL/DC | Clear | 120V | 3000 | 960 | CC-8 | 2 1/4" | Box | 100/10 |
| 60 | T3 | D.C. Bay | S4497 | KX60FR/DC | Frost | 120V | 3000 | 960 | CC-8 | 2 1/4" | Box | 100/10 |

Bi-Pin Lamps

2000 Hours



Frosted Bi Pin

12 Volt

- S1908** 10 Watt
- S1909** 20 Watt
- S1910** 35 Watt
- S1911** 50 Watt
- S1912** 75 Watt

Packing:
Individually Boxed
48/Cartron



Bi Pin

12 Volt

- S3179** 5 Watt
- S3171** 10 Watt
- S3120** 20 Watt
- S3160** 35 Watt
- S3121** 50 Watt
- S3156** 75 Watt

24 Volt

- S1986** 20 Watt
 - S1987** 50 Watt
- Packing: Individually
Boxed, 48/Cartron



Bi Pin

**120 Volt
GY6.35 Base**

- S3197** 25 Watt
- S3164** 35 Watt
- S3167** 50 Watt
- S3168** 75 Watt
- S1924** 100 Watt

Packing:
Individually Boxed
48/Cartron



Bi Pin

**120 Volt (Wide Pin)
G8 Base**

- S4610** 20 Watt
- S4611** 25 Watt
- S4620** 35 Watt
- S4612** 50 Watt
- S4613** 75 Watt
- S4622** 100 Watt

Packing:
Individually Boxed
48/Cartron



Double Loop

**120 Volt
G9 Base**

- S4614** 20 Watt
- S4615** 25 Watt
- S4621** 35 Watt
- S4616** 50 Watt
- S4617** 75 Watt
- S4642** 100 Watt

Packing:
Individually Boxed
48/Cartron

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|--------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 5 | T3 | G4. | S3179 | 5T3 | Clear | 12V | 2000 | 50 | C-6 | 32 MM | Box | 48 |
| 10 | T3 | G4. | S3171 | 10T3 | Clear | 12V | 2000 | 120 | C-6 | 32 MM | Box | 48 |
| 10 | T3 | G4 | S1908 | 10T3/F | Frost | 12V | 2000 | 100 | C-6 | 32 MM | Box | 48 |
| 20 | T3 | G4 | S3120 | 20T3 | Clear | 12V | 2000 | 320 | C-6 | 32 MM | Box | 48 |
| 20 | T3 | G4 | S1909 | 20T3/F | Frost | 12V | 2000 | 300 | C-6 | 32 MM | Box | 48 |
| 20 | T3 | G4 | S1986 | 20T3 | Clear | 24V | 2000 | 260 | C-6 | 32 MM | Box | 48 |
| 20 | T4 | G8 | S4610 | 20T4 | Clear | 120V | 2000 | 180 | C-6 | 46 MM | Box | 48 |
| 20 | T4 | G9 | S4614 | 20T4 | Clear | 120V | 2000 | 180 | C-6 | 45 MM | Box | 48 |
| 25 | T4 | G8 | S4611 | 25T4/F | Clear | 120V | 2000 | 240 | C-6 | 46 MM | Box | 48 |
| 25 | T4 | GY6.35 | S3197 | 25T4 | Clear | 120V | 2000 | 240 | CC-8 | 50 MM | Box | 48 |
| 25 | T4 | G9 | S4615 | 25T4/F | Clear | 120V | 2000 | 240 | C-6 | 45 MM | Box | 48 |
| 35 | T4 | GY6.35 | S3160 | 35T4 | Clear | 12V | 2000 | 600 | C-6 | 41 MM | Box | 48 |
| 35 | T4 | GY6.35 | S1910 | 35T4/F | Frost | 12V | 2000 | 550 | C-6 | 41 MM | Box | 48 |
| 35 | T4 | GY6.35 | S3164 | 35T4 | Clear | 120V | 2000 | 400 | CC-8 | 50 MM | Box | 48 |
| 35 | T4 | G8 | S4620 | 35T4 | Clear | 120V | 2000 | 400 | C-6 | 46 MM | Box | 48 |
| 35 | T4 | G9 | S4621 | 35T4 | Clear | 120V | 2000 | 400 | C-6 | 45 MM | Box | 48 |
| 50 | T4 | G8 | S4612 | 50T4 | Clear | 120V | 2000 | 750 | C-6 | 46 MM | Box | 48 |
| 50 | T4 | GY6.35 | S3121 | 50T4 | Clear | 12V | 2000 | 900 | C-6 | 41 MM | Box | 48 |
| 50 | T4 | GY6.35 | S1911 | 50T4/F | Frost | 12V | 2000 | 850 | C-6 | 41 MM | Box | 48 |
| 50 | T4 | GY6.35 | S1987 | 50T4 | Clear | 24V | 2000 | 850 | C-6 | 41 MM | Box | 48 |
| 50 | T4 | GY6.35 | S3167 | 50T4 | Clear | 120V | 2000 | 750 | CC-8 | 50 MM | Box | 48 |
| 50 | T4 | G9 | S4616 | 50T4 | Clear | 120V | 2000 | 750 | C-6 | 45 MM | Box | 48 |
| 75 | T4 | GY6.35 | S3156 | 75T4 | Clear | 12V | 2000 | 1350 | C-6 | 41 MM | Box | 48 |
| 75 | T4 | GY6.35 | S1912 | 75T4/F | Frost | 12V | 2000 | 1290 | C-6 | 41 MM | Box | 48 |
| 75 | T4 | GY6.35 | S3168 | 75T4 | Clear | 120V | 2000 | 1250 | CC-8 | 60 MM | Box | 48 |
| 75 | T4 | G8 | S4613 | 75T4/F | Clear | 120V | 2000 | 1250 | C-6 | 58 MM | Box | 48 |
| 75 | T4 | G9 | S4617 | 75T4/F | Clear | 120V | 2000 | 1250 | C-6 | 56 MM | Box | 48 |
| 100 | T4 | GY6.35 | S1924 | 100T4 | Clear | 120V | 2000 | 2000 | CC-8 | 60 MM | Box | 48 |
| 100 | T4 | G8 | S4622 | 100T4/F | Clear | 120V | 2000 | 2000 | CC-8 | 58 MM | Box | 48 |

Double Ended Lamps

2000 Hours




78MM J-Type (Short)

| | |
|-----------------------|----------------------|
| 120 Volt | 130 Volt |
| S3199 75 Watt | S3183 75 Watt |
| S3146 100 Watt | Packing: |
| S3135 150 Watt | Individually Boxed, |
| S3145 200 Watt | 12/Master |
| S3184 250 Watt | |



118MM J-Type (Long)

| | |
|-----------------------|-----------------------|
| 120 Volt | 130 Volt |
| S3166 100 Watt | S1925 300 Watt |
| S3142 150 Watt | S1926 500 Watt |
| S3136 200 Watt | Packing: |
| S3104 300 Watt | Individually Boxed, |
| S3105 500 Watt | 12/Master |



254MM J-Type (Long)

240 Volt

S3106 1500 Watt
Packing: Individually Boxed,
12/Master

Flat Blade



145MM J-Type (Blade)

120 Volt

S3180 300 Watt
S1923 500 Watt
Packing: Individually Boxed,
12/Master


Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|--------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 75 | T3 | R7S | S3199 | 75T3Q/CL | Clear | 120V | 2000 | 1200 | C-8 | 3 1/8" | Box | 12 |
| 75 | T3 | R7S | S3183 | 75T3Q/CL | Clear | 130V | 2000 | 1200 | C-8 | 3 1/8" | Box | 12 |
| 100 | T3 | R7S | S3146 | 100T3Q/CL | Clear | 120V | 2000 | 1650 | C-8 | 3 1/8" | Box | 12 |
| 100 | T3 | R7S | S3166 | 100T3Q/CL | Clear | 120V | 2000 | 1650 | C-8 | 4 11/16" | Box | 12 |
| 150 | T3 | R7S | S3135 | 150T3Q/CL | Clear | 120V | 2000 | 2600 | C-8 | 3 1/8" | Box | 12 |
| 150 | T3 | R7S | S3142 | 150T3Q/CL | Clear | 120V | 2000 | 2600 | C-8 | 4 11/16" | Box | 12 |
| 200 | T3 | R7S | S3145 | 200T3Q/CL | Clear | 120V | 2000 | 3200 | C-8 | 3 1/8" | Box | 12 |
| 200 | T3 | R7S | S3136 | 200T3Q/CL | Clear | 120V | 2000 | 3200 | C-8 | 4 11/16" | Box | 12 |
| 250 | T3 | R7S | S3184 | 250T3Q/CL | Clear | 120V | 2000 | 3950 | C-8 | 3 1/8" | Box | 12 |
| 300 | T3 | R7S | S3104 | 300T3Q/CL | Clear | 120V | 2000 | 5000 | C-8 | 4 11/16" | Box | 12 |
| 300 | T3 | R7S | S1925 | 300T3Q/CL | Clear | 130V | 2000 | 5000 | C-8 | 4 11/16" | Box | 12 |
| 300 | T3 | Blade | S3180 | 300T3Q/CL | Clear | 120V | 2000 | 5000 | C-8 | 5 13/16" | Box | 12 |
| 500 | T3 | R7S | S3105 | 500T3Q/CL | Clear | 120V | 2000 | 9500 | C-8 | 4 11/16" | Box | 12 |
| 500 | T3 | R7S | S1926 | 500T3Q/CL | Clear | 130V | 2000 | 9500 | C-8 | 4 11/16" | Box | 12 |
| 500 | T3 | Blade | S1923 | 500T3Q/CL | Clear | 120V | 2000 | 9500 | C-8 | 5 13/16" | Box | 12 |
| 1500 | T3 | R7S | S3106 | 1500T3Q/CL | Clear | 240V | 2000 | 33000 | C-8 | 10 1/16" | Box | 12 |


halogen lamps

2000 Hours


Application Suggestions




Miniature Pendant Fixtures




Vanity Lighting



Cable Systems



Landscape Lighting



Decorative Fixtures



JCGV-14.4

12 Volt
1.8" Diameter
S3187 20W
S3188 35W
S3189 50W
Packing:
Individually Boxed
200/Master, 25/Inner



JCGV-12.8

12 Volt
1.6" Diameter
S3193 20W
Packing:
Individually Boxed
200/Master, 25/Inner

U.L. classified
for U.V. filtration
and particle
containment



JCGV-14.4
Long Neck

12 Volt
1.8" Diameter
S3190 20W
S3191 35W
S3192 50W
Packing:
Individually Boxed
200/Master, 25/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-------------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 20 | GV14.4 | GX5.3 | S3187 | 20JVG2-614 | White | 12V | 2000 | 320 | C-6 | 2.22" | Box | 200/25 |
| 35 | GV14.4 | GX5.3 | S3188 | 35JVG2-614 | White | 12V | 2000 | 620 | C-6 | 2.22" | Box | 200/25 |
| 50 | GV14.4 | GX5.3 | S3189 | 50JVG2-614 | White | 12V | 2000 | 940 | C-6 | 2.22" | Box | 200/25 |
| 20 | GV14.4 | GX5.3 | S3190 | 20JVG2L-614 | White | 12V | 2000 | 320 | C-6 | 2.57" | Box | 200/25 |
| 35 | GV14.4 | GX5.3 | S3191 | 35JVG2L-614 | White | 12V | 2000 | 620 | C-6 | 2.57" | Box | 200/25 |
| 50 | GV14.4 | GX5.3 | S3192 | 50JVG2L-614 | White | 12V | 2000 | 940 | C-6 | 2.57" | Box | 200/25 |
| 20 | GV12.8 | G4 | S3193 | 20JVG2L-614 | White | 12V | 2000 | 340 | C-6 | 2.22" | Box | 200/25 |

halogen lamps

Halogen A-Type Lamps



Post Light

S2647 50 Watt
S1942 75 Watt
 Packing:
 Individually Boxed
 12/Master

Unique faceted bulb provides
 brilliant white halogen light
 for decorative outdoor fixtures.



A-Type

S1943 42 Watt
S2648 42 Watt 130V
S1944 52 Watt
S2649 52 Watt 130V
S1946 60 Watt
S1945 72 Watt
S2650 72 Watt 130V
S1947 75 Watt
S1948 100 Watt

Packing:
 Individually Boxed
 12/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|---|-----------|--------|-----------------|-----------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 42 | A19 | Medium | S1943 | 42A/CAP | Frost | 120V | 3500 | 570 | CC-8 | 4 3/8" | Box | 12 |
| 42 | A19 | Medium | S2648 | 42A/CAP/130 | Frost | 130V | 3500 | 570 | CC-8 | 4 3/8" | Box | 12 |
| 50 | A19 | Medium | S2647 | 50A/HAL/CRYSTAL | Crystal | 120V | 2500 | 860 | CC-8 | 4 3/8" | Box | 12 |
| 52 | A19 | Medium | S1944 | 52A/CAP | Frost | 120V | 3500 | 770 | CC-8 | 4 3/8" | Box | 12 |
| 52 | A19 | Medium | S2649 | 52A/CAP/130 | Frost | 130V | 3500 | 770 | CC-8 | 4 3/8" | Box | 12 |
| 60 | A19 | Medium | S1946 | 60A/HAL | Frost | 120V | 3000 | 960 | CC-8 | 4 3/8" | Box | 12 |
| 72 | A19 | Medium | S1945 | 72A/CAP | Frost | 120V | 3500 | 1150 | CC-8 | 4 3/8" | Box | 12 |
| 72 | A19 | Medium | S2650 | 72A/CAP/130 | Frost | 130V | 3500 | 1150 | CC-8 | 4 3/8" | Box | 12 |
| 75 | A19 | Medium | S1942 | 75A/HAL/CRYSTAL | Crystal | 120V | 3000 | 1330 | CC-8 | 4 3/8" | Box | 12 |
| 75 | A19 | Medium | S1947 | 75A/HAL | Frost | 120V | 3000 | 1300 | CC-8 | 4 3/8" | Box | 12 |
| 100 | A19 | Medium | S1948 | 100A/HAL | Frost | 120V | 3000 | 1800 | CC-8 | 4 3/8" | Box | 12 |
| 130 volt Specifications on 120 Volt Line | | | | | | | | | | | | |
| 37 | A19 | Medium | S2648 | 42A/CAP/130 | Frost | 130V | 7000 | 450 | CC-8 | 4 3/8" | Box | 12 |
| 46 | A19 | Medium | S2649 | 52A/CAP/130 | Frost | 130V | 7000 | 600 | CC-8 | 4 3/8" | Box | 12 |
| 63 | A19 | Medium | S2650 | 72A/CAP/130 | Frost | 130V | 7000 | 900 | CC-8 | 4 3/8" | Box | 12 |

Turn-Tip *Candelabra Base*



Carded Bulbs

1500 Hours / 120 Volt

carded lamps



Clear

S3773 15 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Clear

S3774 25 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Clear

S3762 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Clear

S3775 40 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 15 | CA-8 | Cand. | S3773 | 15CA8 | Clear | 120V | 1500 | 100 | C-7A | 3 5/8" | Card/2 | 120/10 |
| 25 | CA-8 | Cand. | S3774 | 25CA8 | Clear | 120V | 1500 | 210 | CC-2V | 3 5/8" | Card/2 | 120/10 |
| 40 | CA-9 1/2 | Cand. | S3775 | 40CA9 1/2 | Clear | 120V | 1500 | 370 | CC-2V | 3 15/16" | Card/2 | 120/10 |
| 60 | CA-10 | Cand. | S3762 | 60CA10 | Clear | 120V | 1500 | 672 | CC-2V | 4 1/4" | Card/2 | 120/10 |

1500 Hours / 120 Volt

Frosted
S3777 15 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted
S3778 25 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted
S3779 40 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted
S3763 60 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-------------|---------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 15 | CA-8 | Cand. | S3777 | 15CA8/F | Frosted | 120V | 1500 | 90 | C-7A | 3 5/8" | Card/2 | 120/10 |
| 25 | CA-8 | Cand. | S3778 | 25CA8/F | Frosted | 120V | 1500 | 200 | CC-2V | 3 5/8" | Card/2 | 120/10 |
| 40 | CA-9 1/2 | Cand. | S3779 | 40CA9 1/2/F | Frosted | 120V | 1500 | 350 | CC-2V | 3 15/16" | Card/2 | 120/10 |
| 60 | CA-10 | Cand. | S3763 | 60CA10/F | Frosted | 120V | 1500 | 635 | CC-2V | 4 1/4" | Card/2 | 120/10 |

Carded lamps

Torpedo *Candelabra Base*



Carded Bulbs

1500 Hours / 120 Volt

Clear

S3782 25 Watt

S3783 40 Watt

S3784 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted

S3785 25 Watt

S3786 40 Watt

S3787 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Not Shown Actual Size

White

S3788 25 Watt

S3789 40 Watt

S3790 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B9 1/2 | Cand. | S3782 | 25B9 1/2 | Clear | 120V | 1500 | 212 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 25 | B9 1/2 | Cand. | S3785 | 25B9 1/2/F | Frosted | 120V | 1500 | 212 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 25 | B9 1/2 | Cand. | S3788 | 25B9 1/2/W | White | 120V | 1500 | 180 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 40 | B9 1/2 | Cand. | S3783 | 40B9 1/2 | Clear | 120V | 1500 | 384 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 40 | B9 1/2 | Cand. | S3786 | 40B9 1/2/F | Frosted | 120V | 1500 | 384 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 40 | B9 1/2 | Cand. | S3789 | 40B9 1/2/W | White | 120V | 1500 | 328 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 60 | B10 | Cand. | S3784 | 60B10 | Clear | 120V | 1500 | 672 | CC-2V | 3 3/4" | Card/2 | 120/10 |
| 60 | B10 | Cand. | S3787 | 60B10/F | Frosted | 120V | 1500 | 672 | CC-2V | 3 3/4" | Card/2 | 120/10 |
| 60 | B10 | Cand. | S3790 | 60B10/W | White | 120V | 1500 | 630 | CC-2V | 3 3/4" | Card/2 | 120/10 |

carded lamps

1500 Hours / 120 Volt



Clear

S3764 25 Watt
S3765 40 Watt
S3766 60 Watt
 Packing: 2 Bulbs/Card
 120 Cards/Master,
 10 Cards/Inner




Frosted

S3767 25 Watt
S3768 40 Watt
S3769 60 Watt
 Packing: 2 Bulbs/Card
 120 Cards/Master,
 10 Cards/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | CA-10 | Med. | S3764 | 25CA10 | Clear | 120V | 1500 | 210 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 25 | CA-10 | Med. | S3767 | 25CA10/F | Frosted | 120V | 1500 | 200 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 40 | CA-10 | Med. | S3765 | 40CA10 | Clear | 120V | 1500 | 370 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 40 | CA-10 | Med. | S3768 | 40CA10/F | Frosted | 120V | 1500 | 360 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 60 | CA-10 | Med. | S3766 | 60CA10 | Clear | 120V | 1500 | 650 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 60 | CA-10 | Med. | S3769 | 60CA10/F | Frosted | 120V | 1500 | 640 | CC-2V | 4 1/4" | Card/2 | 120/10 |

Carded lamps



Torpedo *Medium Base*

Carded Bulbs



1500 Hours / 120 Volt



Clear

S3731 25 Watt
S3732 40 Watt
S3793 60 Watt
 Packing: 2 Bulbs/Card
 120 Cards/Master,
 10 Cards/Inner



Frosted

S3734 25 Watt
S3735 40 Watt
S3796 60 Watt
 Packing: 2 Bulbs/Card
 120 Cards/Master,
 10 Cards/Inner



White

S3737 25 Watt
S3738 40 Watt
S3799 60 Watt
 Packing: 2 Bulbs/Card
 120 Cards/Master,
 10 Cards/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B11 | Med. | S3731 | 25B11 | Clear | 120V | 1500 | 210 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 25 | B11 | Med. | S3734 | 25B11/F | Frosted | 120V | 1500 | 200 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 25 | B11 | Med. | S3737 | 25B11/W | White | 120V | 1500 | 150 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B11 | Med. | S3732 | 40B11 | Clear | 120V | 1500 | 370 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B11 | Med. | S3735 | 40B11/F | Frosted | 120V | 1500 | 360 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B11 | Med. | S3738 | 40B11/W | White | 120V | 1500 | 330 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B11 | Med. | S3793 | 60B11 | Clear | 120V | 1500 | 650 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B11 | Med. | S3796 | 60B11/F | Frosted | 120V | 1500 | 640 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B11 | Med. | S3799 | 60B11/W | White | 120V | 1500 | 580 | CC-2V | 3 7/8" | Card/2 | 120/10 |

carded lamps

1500 Hours / 120 Volt



Clear

Frosted

E14
European Base

- S4711 25 Watt
- S4712 40 Watt
- S4713 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner

specialty
product

E14
European Base

- S4714 25 Watt
- S4715 40 Watt
- S4716 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B9 1/2 | Euro. | S4711 | 25B9 1/2 | Clear | 120V | 1500 | 212 | CC-2V | 3 1/2" | Card/2 | 120/12 |
| 25 | B9 1/2 | Euro. | S4714 | 25B9 1/2/F | Frosted | 120V | 1500 | 212 | CC-2V | 3 1/2" | Card/2 | 120/12 |
| 40 | B9 1/2 | Euro. | S4712 | 40B9 1/2 | Clear | 120V | 1500 | 384 | CC-2V | 3 1/2" | Card/2 | 120/12 |
| 40 | B9 1/2 | Euro. | S4715 | 40B9 1/2/F | Frosted | 120V | 1500 | 384 | CC-2V | 3 1/2" | Card/2 | 120/12 |
| 60 | B10 | Euro. | S4713 | 60B10 | Clear | 120V | 1500 | 672 | CC-2V | 3 3/4" | Card/2 | 120/12 |
| 60 | B10 | Euro. | S4716 | 60B10/F | Frosted | 120V | 1500 | 672 | CC-2V | 3 3/4" | Card/2 | 120/12 |



Turn-Tip *Candelabra Base*

ALLURA®

Carded Bulbs

2500 Hours / 130 Volt

carded lamps

Clear

A3573 15 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Clear

A3574 25 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Clear

A3562 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Clear

A3575 40 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 15 | CA-8 | Cand. | A3573 | 15CA8 | Clear | 130V | 2500 | 95 | C-7A | 3 5/8" | Card/2 | 120/10 |
| 25 | CA-8 | Cand. | A3574 | 25CA8 | Clear | 130V | 2500 | 360 | CC-2V | 3 5/8" | Card/2 | 120/10 |
| 40 | CA-9 1/2 | Cand. | A3575 | 40CA9 1/2 | Clear | 130V | 2500 | 370 | CC-2V | 3 15/16" | Card/2 | 120/10 |
| 60 | CA-10 | Cand. | A3562 | 60CA10 | Clear | 130V | 2500 | 642 | CC-2V | 4 1/4" | Card/2 | 120/10 |

2500 Hours / 130 Volt



Frosted
A3577 15 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted
A3578 25 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted
A3579 40 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted
A3563 60 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



carded lamps

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|---------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 15 | CA-8 | Cand. | A3577 | 15CA8 | Frosted | 130V | 2500 | 90 | C-7A | 3 5/8" | Card/2 | 120/10 |
| 25 | CA-8 | Cand. | A3578 | 25CA8 | Frosted | 130V | 2500 | 200 | CC-2V | 3 5/8" | Card/2 | 120/10 |
| 40 | CA-9 1/2 | Cand. | A3579 | 40CA9 1/2 | Frosted | 130V | 2500 | 350 | CC-2V | 3 15/16" | Card/2 | 120/10 |
| 60 | CA-10 | Cand. | A3563 | 60CA10 | Frosted | 130V | 2500 | 635 | CC-2V | 4 1/4" | Card/2 | 120/10 |



Torpedo *Candelabra Base*

ALLURA®

Carded Bulbs

2500 Hours / 130 Volt

carded lamps

Clear

A3582 25 Watt

A3583 40 Watt

A3584 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted

A3585 25 Watt

A3586 40 Watt

A3587 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



White

A3588 25 Watt

A3589 40 Watt

A3590 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B9 1/2 | Cand. | A3582 | 25B9 1/2 | Clear | 130V | 2500 | 193 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 25 | B9 1/2 | Cand. | A3585 | 25B9 1/2/F | Frosted | 130V | 2500 | 193 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 25 | B9 1/2 | Cand. | A3588 | 25B9 1/2/W | White | 130V | 2500 | 163 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 40 | B9 1/2 | Cand. | A3583 | 40B9 1/2 | Clear | 130V | 2500 | 384 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 40 | B9 1/2 | Cand. | A3586 | 40B9 1/2/F | Frosted | 130V | 2500 | 384 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 40 | B9 1/2 | Cand. | A3589 | 40B9 1/2/W | White | 130V | 2500 | 328 | CC-2V | 3 1/2" | Card/2 | 120/10 |
| 60 | B10 | Cand. | A3584 | 60B10 | Clear | 130V | 2500 | 642 | CC-2V | 3 3/4" | Card/2 | 120/10 |
| 60 | B10 | Cand. | A3587 | 60B10/F | Frosted | 130V | 2500 | 642 | CC-2V | 3 3/4" | Card/2 | 120/10 |
| 60 | B10 | Cand. | A3590 | 60B10/W | White | 130V | 2500 | 564 | CC-2V | 3 3/4" | Card/2 | 120/10 |

2500 Hours / 130 Volt



Clear

- A3564** 25 Watt
- A3565** 40 Watt
- A3566** 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Frosted

- A3567** 25 Watt
- A3568** 40 Watt
- A3569** 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



carded lamps

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | CA-10 | Med. | A3564 | 25CA10 | Clear | 130V | 2500 | 210 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 25 | CA-10 | Med. | A3567 | 25CA10/F | Frosted | 130V | 2500 | 200 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 40 | CA-10 | Med. | A3565 | 40CA10 | Clear | 130V | 2500 | 370 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 40 | CA-10 | Med. | A3568 | 40CA10/F | Frosted | 130V | 2500 | 360 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 60 | CA-10 | Med. | A3566 | 60CA10 | Clear | 130V | 2500 | 650 | CC-2V | 4 1/4" | Card/2 | 120/10 |
| 60 | CA-10 | Med. | A3569 | 60CA10/F | Frosted | 130V | 2500 | 640 | CC-2V | 4 1/4" | Card/2 | 120/10 |

Torpedo *Medium Base*

Carded Bulbs **ALLURA**[®]

2500 Hours / 130 Volt

carded lamps



White

A3537 25 Watt
A3538 40 Watt
A3599 60 Watt
 Packing: 2 Bulbs/Card
 120 Cards/Master,
 10 Cards/Inner



Frosted

A3534 25 Watt
A3535 40 Watt
A3596 60 Watt
 Packing: 2 Bulbs/Card
 120 Cards/Master,
 10 Cards/Inner



Clear

A3531 25 Watt
A3532 40 Watt
A3593 60 Watt
 Packing: 2 Bulbs/Card
 120 Cards/Master,
 10 Cards/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | B11 | Med. | A3531 | 25B11 | Clear | 130V | 2500 | 210 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 25 | B11 | Med. | A3534 | 25B11/F | Frosted | 130V | 2500 | 200 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 25 | B11 | Med. | A3537 | 25B11/W | White | 130V | 2500 | 160 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B11 | Med. | A3532 | 40B11 | Clear | 130V | 2500 | 370 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B11 | Med. | A3535 | 40B11/F | Frosted | 130V | 2500 | 360 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B11 | Med. | A3538 | 40B11/W | White | 130V | 2500 | 320 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B11 | Med. | A3593 | 60B11 | Clear | 130V | 2500 | 650 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B11 | Med. | A3596 | 60B11/F | Frosted | 130V | 2500 | 640 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B11 | Med. | A3599 | 60B11/W | White | 130V | 2500 | 550 | CC-2V | 3 7/8" | Card/2 | 120/10 |

Candelabra Base Globe

Carded Bulbs

1500 Hours / 120 Volt



G16 1/2 2 1/8"

Clear
Candelabra Base
(120 Volt)

- S3726** 15 Watt
- S3727** 25 Watt
- S3728** 40 Watt
- S3771** 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



G16 1/2 2 1/8"

Satin White
Candelabra Base
(120 Volt)

- S3752** 15 Watt
- S3753** 25 Watt
- S3754** 40 Watt
- S3772** 60 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



G12 1 1/2"

Satin White
Candelabra Base
(120 Volt)

- S3755** 10 Watt
- S3750** 15 Watt
- S3751** 25 Watt

Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./Inner Pack |
|-------|-----------|-------|-----------------|-------------|------------|-------|------------------|--------|----------|--------|------------|---------------------|
| 10 | G12 | Cand. | S3755 | 10G12/W | Sat. White | 120V | 1500 | 60 | C7A | 2 3/8" | Card/2 | 120/10 |
| 15 | G12 | Cand. | S3750 | 15G12/W | Sat. White | 120V | 1500 | 94 | C7A | 2 3/8" | Card/2 | 120/10 |
| 15 | G16 1/2 | Cand. | S3726 | 15G16 1/2 | Clear | 120V | 1500 | 114 | C7A | 3" | Card/2 | 120/10 |
| 15 | G16 1/2 | Cand. | S3752 | 15G16 1/2/W | Sat. White | 120V | 1500 | 94 | C7A | 3" | Card/2 | 120/10 |
| 25 | G12 | Cand. | S3751 | 25G12/W | Sat. White | 120V | 1500 | 202 | C7A | 2 3/8" | Card/2 | 120/10 |
| 25 | G16 1/2 | Cand. | S3727 | 25G16 1/2 | Clear | 120V | 1500 | 232 | CC-2V | 3" | Card/2 | 120/10 |
| 25 | G16 1/2 | Cand. | S3753 | 25G16 1/2/W | Sat. White | 120V | 1500 | 202 | CC-2V | 3" | Card/2 | 120/10 |
| 40 | G16 1/2 | Cand. | S3728 | 40G16 1/2 | Clear | 120V | 1500 | 384 | CC-2V | 3" | Card/2 | 120/10 |
| 40 | G16 1/2 | Cand. | S3754 | 40G16 1/2/W | Sat. White | 120V | 1500 | 348 | CC-2V | 3" | Card/2 | 120/10 |
| 60 | G16 1/2 | Cand. | S3771 | 60G16 1/2 | Clear | 120V | 1500 | 672 | CC-2V | 3" | Card/2 | 120/10 |
| 60 | G16 1/2 | Cand. | S3772 | 60G16 1/2/W | Sat. White | 120V | 1500 | 630 | CC-2V | 3" | Card/2 | 120/10 |

carded lamps



Carded Bulbs

carded lamps

G14 Clear
E14 Euro Base
(130 Volt)
S4707 40 Watt
Packing: 2 Bulbs /Card
120 Cards/Master,
10 Cards/Inner



G14 White
E14 Euro Base
(130 Volt)
S4708 40 Watt
Packing:
2 Bulbs /Card
120 Cards/Master,
10 Cards/Inner



G16^{1/2} Globe Light Clear
Medium Base 120V
S4538 25 Watt Clear
S4539 40 Watt Clear
S4540 60 Watt Clear
Packing: 1/Card
120/Master, 10/Inner



G16^{1/2} Globe Light White
Medium Base 120V
S4541 25 Watt White
S4542 40 Watt White
S4543 60 Watt White
Packing: 1/Card
120/Master, 10/Inner



G17 Frosted
Medium Base
(130 Volt)
S4709 40 Watt
Packing: 1 Bulb /Card
120 Cards/Master,
10 Cards/Inner



G17 White
Medium Base
(130 Volt)
S4710 40 Watt
Packing:
1 Bulb /Card
120 Cards/Master,
10 Cards/Inner



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 40 | G14 | Euro | S4707 | 40G14 | Clear | 130V | 1000 | 360 | CC-2V | 2 5/8" | Card/2 | 120/10 |
| 40 | G14 | Euro | S4708 | 40G14/W | White | 130V | 1000 | 320 | CC-2V | 2 5/8" | Card/2 | 120/10 |
| 25 | G16 | Med. | S4538 | 25G16 | Clear | 120V | 1500 | 210 | CC-2V | 3 1/4" | Card/1 | 120/10 |
| 25 | G16 | Med. | S4541 | 25G16/W | White | 120V | 1500 | 160 | CC-2V | 3 1/4" | Card/1 | 120/10 |
| 40 | G16 | Med. | S4539 | 40G16 | Clear | 120V | 1500 | 370 | CC-2V | 3 1/4" | Card/1 | 120/10 |
| 40 | G16 | Med. | S4542 | 40G16/W | White | 120V | 1500 | 320 | CC-2V | 3 1/4" | Card/1 | 120/10 |
| 60 | G16 | Med. | S4540 | 60G16 | Clear | 120V | 1500 | 650 | CC-2V | 3 1/4" | Card/1 | 120/10 |
| 60 | G16 | Med. | S4543 | 60G16/W | White | 120V | 1500 | 550 | CC-2V | 3 1/4" | Card/1 | 120/10 |
| 40 | G17 | Med. | S4709 | 40G17/F | Frosted | 130V | 1000 | 348 | CC-2V | 3 1/4" | Card/1 | 120/10 |
| 40 | G17 | Med. | S4710 | 40G17/W | White | 130V | 1000 | 348 | CC-2V | 3 1/4" | Card/1 | 120/10 |

2500 Hours / 130 Volt



Clear
Candelabra Base
(130 Volt)
A3521 15 Watt
A3522 25 Watt
A3523 40 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Satin White
Candelabra Base
(130 Volt)
A3524 15 Watt
A3525 25 Watt
A3526 40 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner



Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-------------|--------|-------|------------------|--------|----------|--------|------------|----------------------|
| 15 | G16 1/2 | Cand. | A3521 | 15G16 1/2 | Clear | 130V | 2500 | 98 | C7A | 3" | Card/2 | 120/10 |
| 15 | G16 1/2 | Cand. | A3524 | 15G16 1/2/W | White | 130V | 2500 | 83 | C7A | 3" | Card/2 | 120/10 |
| 25 | G16 1/2 | Cand. | A3522 | 25G16 1/2 | Clear | 130V | 2500 | 186 | C7A | 3" | Card/2 | 120/10 |
| 25 | G16 1/2 | Cand. | A3525 | 25G16 1/2/W | White | 130V | 2500 | 162 | C7A | 3" | Card/2 | 120/10 |
| 40 | G16 1/2 | Cand. | A3523 | 40G16 1/2 | Clear | 130V | 2500 | 360 | CC-2V | 3" | Card/2 | 120/10 |
| 40 | G16 1/2 | Cand. | A3526 | 40G16 1/2/W | White | 130V | 2500 | 325 | CC-2V | 3" | Card/2 | 120/10 |

carded lamps



Carded Bulbs

4000 Hours / 120 Volt

carded lamps



C11 Satin



C11 Amber



C15

Candelabra Base
(120 Volt)

- S2703** 25 Watt
- S2704** 40 Watt
- S2705** 60 Watt

Packing: 1 Bulb/Card
120 Cards/Master,
12 Cards/Inner

Candelabra Base
(120 Volt)

- S2706** 25 Watt
- Packing: 1 Bulb/Card
120 Cards/Master,
12 Cards/Inner

Medium Base
(120 Volt)

- S2713** 25 Watt
- S2714** 40 Watt
- S2715** 60 Watt
- S2716** 40 Watt Amber

Packing: 1 Bulb/Card
120 Cards/Master,
12 Cards/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|----------------------|
| 25 | C11 | Cand. | S2703 | 25C11 | Satin | 120V | 4000 | 160 | C-7A | 4" | Card/1 | 120/12 |
| 25 | C11 | Cand. | S2706 | 25C11/A | Amber | 120V | 4000 | - | C-7A | 4" | Card/1 | 120/12 |
| 40 | C11 | Cand. | S2704 | 40C11 | Satin | 120V | 4000 | 316 | C-7A | 4" | Card/1 | 120/12 |
| 60 | C11 | Cand. | S2705 | 60C11 | Satin | 120V | 4000 | 600 | C-7A | 4" | Card/1 | 120/12 |
| 25 | C15 | Med. | S2713 | 25C15 | Satin | 120V | 4000 | 160 | C-9 | 4 1/2" | Card/1 | 120/12 |
| 40 | C15 | Med. | S2714 | 40C15 | Satin | 120V | 4000 | 316 | C-9 | 4 1/2" | Card/1 | 120/12 |
| 40 | C15 | Med. | S2716 | 40C15/A | Amber | 120V | 4000 | 316 | C-9 | 4 1/2" | Card/1 | 120/12 |
| 60 | C15 | Med. | S2715 | 60C15 | Satin | 120V | 4000 | 606 | C-9 | 4 1/2" | Card/1 | 120/12 |

1500 Hours

Not Shown Actual Size



Clear

S2760 15 Watt
S2771 25 Watt



White

S2761 15 Watt
S2772 25 Watt



Aurora

S2773 25 Watt



Amber

S2774 25 Watt



F10

Candelabra Base
(120 Volt)

Packing: 2 Bulbs to a Card
120 Cards /Master, 12 Cards / Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|---------|------------|----------------------|
| 15 | F10 | Cand. | S2760 | 15F10 | Clear | 120V | 1500 | 110 | C-7A | 3 1/16" | Card/2 | 120/12 |
| 15 | F10 | Cand. | S2761 | 15F10/W | White | 120V | 1500 | 90 | C-7A | 3 1/16" | Card/2 | 120/12 |
| 25 | F10 | Cand. | S2771 | 25F10 | Clear | 120V | 1500 | 195 | C-7A | 3 1/16" | Card/2 | 120/12 |
| 25 | F10 | Cand. | S2772 | 25F10/W | White | 120V | 1500 | 185 | C-7A | 3 1/16" | Card/2 | 120/12 |
| 25 | F10 | Cand. | S2773 | 25F10/AU | Aurora | 120V | 1500 | 190 | C-7A | 3 1/16" | Card/2 | 120/12 |
| 25 | F10 | Cand. | S2774 | 25F10/A | Amber | 120V | 1500 | - | C-7A | 3 1/16" | Card/2 | 120/12 |

carded lamps



F15 Flame Brass Base



Carded Bulbs

1500 Hours

carded lamps



F15

Medium Base
(120 Volt)

- S2763** 25 Watt Clear
- S2767** 40 Watt Clear
- S2764** 25 Watt White
- S2768** 40 Watt White
- S2765** 25 Watt Aurora
- S2769** 40 Watt Aurora
- S2770** 40 Watt Amber

Packing: 2 Bulbs to a Card
120 Cards/Master,
12 Cards/Inner



White



Clear




Aurora



Amber

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 25 | F15 | Med. | S2763 | 25F15 | Clear | 120V | 1500 | 225 | CC-9 | 4 1/2" | Card/2 | 120/12 |
| 25 | F15 | Med. | S2764 | 25F15/W | White | 120V | 1500 | 195 | CC-9 | 4 1/2" | Card/2 | 120/12 |
| 25 | F15 | Med. | S2765 | 25F15/AU | Aurora | 120V | 1500 | 200 | CC-9 | 4 1/2" | Card/2 | 120/12 |
| 40 | F15 | Med. | S2767 | 40F15 | Clear | 120V | 1500 | 420 | CC-9 | 4 1/2" | Card/2 | 120/12 |
| 40 | F15 | Med. | S2768 | 40F15/W | White | 120V | 1500 | 372 | CC-9 | 4 1/2" | Card/2 | 120/12 |
| 40 | F15 | Med. | S2769 | 40F15/AU | Aurora | 120V | 1500 | 420 | CC-9 | 4 1/2" | Card/2 | 120/12 |
| 40 | F15 | Med. | S2770 | 40F15/A | Amber | 120V | 1500 | - | CC-9 | 4 1/2" | Card/2 | 120/12 |



Krypton

**Torpedo
Clear**

Candelabra Base
(120 Volt)

S3716 25 Watt

S3717 40 Watt

S3718 60 Watt

Packing: Card/2
120/Master, 10/Inner

Krypton

decorative bulbs

create a brilliant sparkle,
similar to the look of halogen .

Excellent for use in crystal
chandeliers and fixtures with
decorative glassware.

Additionally , krypton bulbs
last longer than conventional
lamps and maintain their
lumen output during the
full course of their life.



Diamond Cut

**Torpedo
Clear**

Candelabra Base
(120 Volt)

S3725 40 Watt

Packing: Card/2
120/Master, 10/Inner

Diamond Cut

decorative bulbs

simulate the look of an
illuminated crystal prism.
These lamps will add a
unique effect when used
with crystal chandeliers.



Silicone

S4520 5 Watt
Packing: Card/2
144/Master, 12/Inner

Silicone

decorative bulbs

silicone dipped,
perfect for decorative
candle sconces and
portable candle lamps.

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|--------------|----------|-------|------------------|--------|----------|---------|------------|----------------------|
| 5 | C7 | Cand. | S4520 | 5C7 | Silicone | 120V | 1000 | 10 | C-7A | 2 1/2+" | Card/2 | 144/12 |
| 25 | B9 1/2 | Cand. | S3716 | KR25B9 1/2 | Clear | 120V | 2500 | 210 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B9 1/2 | Cand. | S3717 | KR40B9 1/2 | Clear | 120V | 2500 | 370 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B10 | Cand. | S3718 | KR60B10 | Clear | 120V | 2500 | 640 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B9 1/2 | Cand. | S3725 | 40B9 1/2/DIA | Clear | 120V | 1500 | 370 | CC-2V | 3 7/8" | Card/2 | 120/10 |

carded lamps

Ceiling *Brass Base* Fan Bulbs



2000 Hours

- High temperature base cement
- Vibration resistant filament

carded lamps



Clear



Frosted

S4740 40 Watt
S4741 60 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner

S4742 40 Watt
S4743 60 Watt
Packing: 2 Bulbs/Card
120 Cards/Master,
10 Cards/Inner

Shown Actual Size


| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-------------|---------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 40 | B11 | Med. | S4740 | 40B11/Fan | Clear | 120V | 2000 | 370 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 40 | B11 | Med. | S4742 | 40B11/Fan/F | Frosted | 120V | 2000 | 360 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B11 | Med. | S4741 | 60B11/Fan | Clear | 120V | 2000 | 650 | CC-2V | 3 7/8" | Card/2 | 120/10 |
| 60 | B11 | Med. | S4743 | 60B11/Fan/F | Frosted | 120V | 2000 | 640 | CC-2V | 3 7/8" | Card/2 | 120/10 |



Brass Base Prismatic

1500 Hours / 120 Volt

Carded Bulbs



Aurora



Frosted



Clear

Candelabra Base
(120 Volt)

S3748 25 Watt
S3749 40 Watt

Packing:
2 Bulbs to a Card
120 Cards/Master,
12 Cards/Inner

Candelabra Base
(120 Volt)

S3746 25 Watt
S3747 40 Watt

Packing:
2 Bulbs to a Card
120 Cards/Master,
12 Cards/Inner

Candelabra Base
(120 Volt)

S3744 25 Watt
S3745 40 Watt

Packing:
2 Bulbs to a Card
120 Cards/Master,
12 Cards/Inner

*Not Shown
Actual Size*

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Volts | Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|--------------|---------|------------------|-------------|--------|----------|----------|------------|-----------------------|
| 25 | HX-101/2 | Cand. | S3744 | 25HX101/2 | Clear | 120V | 1500 | 175 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 25 | HX-101/2 | Cand. | S3746 | 25HX101/2/F | Frosted | 120V | 1500 | 175 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 25 | HX-101/2 | Cand. | S3748 | 25HX101/2/AU | Aurora | 120V | 1500 | 175 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 40 | HX-101/2 | Cand. | S3745 | 40HX101/2 | Clear | 120V | 1500 | 360 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 40 | HX-101/2 | Cand. | S3747 | 40HX101/2/F | Frosted | 120V | 1500 | 360 | C-7A | 4 15/16" | Card/2 | 120/12 |
| 40 | HX-101/2 | Cand. | S3749 | 40HX101/2/AU | Aurora | 120V | 1500 | 360 | C-7A | 4 15/16" | Card/2 | 120/12 |

Carded lamps

Carded Bulbs

1000 Hours /120 Volt



Candelabra Base
S3756 3 Watt



Candelabra Base
S3759 3 Watt



Medium Base
S3757 3 Watt



Medium Base
S3760 3 Watt



Candelabra Base
S3761 3 Watt



Shown
Actual Size

Packing:
1 Bulb to a Card
120 Cards/Master,
12 Cards/Inner

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|--------------|--------|-------|------------------|--------|----------|---------|------------|----------------------|
| 3 | CA-5 1/2 | Cand. | S3761 | 3CA5 1/2/FLK | Clear | 120V | 1000 | - | Flicker | 3 1/4" | Card/1 | 120/12 |
| 3 | CA-8 | Cand. | S3756 | 3CA8/FLK | Clear | 120V | 1000 | - | Flicker | 3 7/8" | Card/1 | 120/12 |
| 3 | B-9 1/2 | Cand. | S3759 | 3B9 1/2/FLK | Clear | 120V | 1000 | - | Flicker | 3 1/2" | Card/1 | 120/12 |
| 3 | CA-10 | Med. | S3757 | 3CA10/FLK | Clear | 120V | 1000 | - | Flicker | 4 1/16" | Card/1 | 120/12 |
| 3 | CA-9 | Med. | S3760 | 3CA9/FLK | Clear | 120V | 1000 | - | Flicker | 4 9/16" | Card/1 | 120/12 |

carded lamps



T6 1/2



T6 1/2



T10



Intermediate Base
(130 Volt)
S3709 25 Watt Clear
S3708 25 Watt Frosted
S3710 40 Watt Clear
S3712 40 Watt Frosted
 Packing: 1 Bulb to a Card
 120 Cards/Master,
 10 Cards/Inner

D.C. Bayonet Base
(130 Volt)
S3711 25 Watt Clear
S3713 25 Watt Frosted
 Packing:
 1 Bulb to a Card
 120 Cards/Master,
 10 Cards/Inner

Medium Base
(120 Volt)
S3700 25 Watt Clear
S3701 25 Watt Frosted
S3702 40 Watt Clear
S3703 40 Watt Frosted
S3704 60 Watt Clear
S3705 60 Watt Frosted
 Packing: 1 Bulb to a Card
 120 Cards/Master,
 10 Cards/Inner

Not Shown
Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|--------|-----------------|---------------|---------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 25 | T6 1/2 | DC Bay | S3711 | 25T6 1/2 DC | Clear | 130V | 1500 | 180 | C-8 | 5 3/8" | Card/1 | 120/10 |
| 25 | T6 1/2 | DC Bay | S3713 | 25T6 1/2 DC/F | Frosted | 130V | 1500 | 170 | C-8 | 5 3/8" | Card/1 | 120/10 |
| 25 | T6 1/2 | Int. | S3709 | 25T6 1/2 N | Clear | 130V | 1500 | 180 | C-8 | 5 3/8" | Card/1 | 120/10 |
| 25 | T6 1/2 | Int. | S3708 | 25T6 1/2 N/F | Frosted | 130V | 1500 | 170 | C-8 | 5 3/8" | Card/1 | 120/10 |
| 40 | T6 1/2 | Int. | S3710 | 40T6 1/2 N | Clear | 130V | 1500 | 350 | C-8 | 5 3/8" | Card/1 | 120/10 |
| 40 | T6 1/2 | Int. | S3712 | 40T6 1/2 N/F | Frosted | 130V | 1500 | 340 | C-8 | 5 3/8" | Card/1 | 120/10 |
| 25 | T10 | Med. | S3700 | 25T10 | Clear | 120V | 1000 | 210 | C-5V | 5 3/16" | Card/1 | 120/10 |
| 25 | T10 | Med. | S3701 | 25T10/F | Frosted | 120V | 1000 | 200 | C-5V | 5 3/16" | Card/1 | 120/10 |
| 40 | T10 | Med. | S3702 | 40T10 | Clear | 120V | 1000 | 300 | C-5V | 5 3/16" | Card/1 | 120/10 |
| 40 | T10 | Med. | S3703 | 40T10/F | Frosted | 120V | 1000 | 290 | C-5V | 5 3/16" | Card/1 | 120/10 |
| 60 | T10 | Med. | S3704 | 60T10 | Clear | 120V | 1000 | 490 | C-5V | 5 3/16" | Card/1 | 120/10 |
| 60 | T10 | Med. | S3705 | 60T10/F | Frosted | 120V | 1000 | 480 | C-5V | 5 3/16" | Card/1 | 120/10 |

Carded lamps

Specialty Carded Bulbs



Not Shown Actual Size



**Hi Intensity
S3723**
12 Watt/15CP
SC Bayonet Base
12-16V
Dom. Code #93
Packing: 2 /Card
240/Master, 20/Inner



**Hi Intensity
S3729**
40 Watt
Intermediate Base
115-125V
Dom. Code #40S11N
Packing: 2 /Card
240/Master, 20/Inner



**Hi Intensity
S3724**
24 Watt/32 CP
SC Bayonet Base
6-8V
Dom. Code #1133
Packing: 2 /Card
240/Master, 20/Inner



7 1/2 S11
Medium Base
(120 Volt)
S3794 7 1/2 Watt Clear
S3795 7 1/2 Watt White
Packing: 1 Bulb/Card
240 Cards/Master,
20 Cards/Inner



**S11 Ceramic
Colored Bulbs**
Medium Base 120V
S4508 7 1/2 Watt Blue
S4509 7 1/2 Watt Green
S4510 7 1/2 Watt Orange
S4511 7 1/2 Watt Red
S4512 7 1/2 Watt Yellow
Packing: 1/Card
120/Master, 10/Inner



**S14 Ceramic
Colored Bulbs**
Medium Base 130V
S4560 11 Watt Yellow
S4561 11 Watt Red
S4562 11 Watt Green
S4563 11 Watt Blue
S4564 11 Watt Orange
S4565 11 Watt Clear
S4566 11 Watt White
Packing: 1/Card
120/Master, 10/Inner



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|---------------|-----------------|-------------|--------|----------|------------------|--------|----------|--------|------------|----------------------|
| 7 1/2 | S11 | Med. | S3794 | 7 1/2 S11 | Clear | 120V | 2500 | 40 | C-7A | 2 1/4" | Card/1 | 240/20 |
| 7 1/2 | S11 | Med. | S3795 | 7 1/2 S11/W | White | 120V | 2500 | 20 | C-7A | 2 1/4" | Card/1 | 240/20 |
| 7 1/2 | S11 | Med. | S4508 | 7 1/2 S11/B | Blue | 120V | 2500 | - | C-7A | 2 1/4" | 1/Card | 120/10 |
| 7 1/2 | S11 | Med. | S4509 | 7 1/2 S11/G | Green | 120V | 2500 | - | C-7A | 2 1/4" | 1/Card | 120/10 |
| 7 1/2 | S11 | Med. | S4510 | 7 1/2 S11/O | Orange | 120V | 2500 | - | C-7A | 2 1/4" | 1/Card | 120/10 |
| 7 1/2 | S11 | Med. | S4511 | 7 1/2 S11/R | Red | 120V | 2500 | - | C-7A | 2 1/4" | 1/Card | 120/10 |
| 7 1/2 | S11 | Med. | S4512 | 7 1/2 S11/Y | Yellow | 120V | 2500 | - | C-7A | 2 1/4" | 1/Card | 120/10 |
| 11 | S14 | Med. | S4560 | 11S14/Y | Yellow | 130V | 2500 | 80 | CC-9 | 3 1/2" | 1/Card | 120/10 |
| 11 | S14 | Med. | S4561 | 11S14/R | Red | 130V | 2500 | 65 | CC-9 | 3 1/2" | 1/Card | 120/10 |
| 11 | S14 | Med. | S4562 | 11S14/G | Green | 130V | 2500 | - | CC-9 | 3 1/2" | 1/Card | 120/10 |
| 11 | S14 | Med. | S4563 | 11S14/B | Blue | 130V | 2500 | - | CC-9 | 3 1/2" | 1/Card | 120/10 |
| 11 | S14 | Med. | S4564 | 11S14/O | Orange | 130V | 2500 | - | CC-9 | 3 1/2" | 1/Card | 120/10 |
| 11 | S14 | Med. | S4565 | 11S14 | Clear | 130V | 2500 | - | CC-9 | 3 1/2" | 1/Card | 120/10 |
| 11 | S14 | Med. | S4566 | 11S14/W | White | 130V | 2500 | - | CC-9 | 3 1/2" | 1/Card | 120/10 |
| 12 | S8 | S.C BAY/BA15S | S3723 | 12S8/93 | Clear | 12-16V | 300 | 190 | C-6 | 2 " | 2/Card | 240/20 |
| 24 | RP11 | S.C BAY/BA15S | S3724 | 24RP11/33 | Clear | 6-8V | 300 | 400 | C-6 | 2 1/4" | 2/Card | 240/20 |
| 40 | S11 | E17/Int. | S3729 | 40S11/N | Clear | 115/125V | 1500 | 370 | CC-2V | 2 3/8" | 1/Card | 240/20 |

carded lamps

Night Light & Appliance Bulbs *Carded*



40A15/60A15

Medium Base
(130 Volt)
S3720 40 Watt Clear
S3721 40 Watt Frosted
S3739 60 Watt Clear
S3740 60 Watt Frosted
 Packing: 1 Bulb/Card
 240 Cards/Master,
 20 Cards/Inner



7C7 & 4C7

Candelabra Base
(120 Volt)

Two Pack

S3797 4 Watt Clear
S3791 7 Watt Clear
S3792 7 Watt White

Packing: 2 Bulbs/Card
 400 Cards/Master,
 20 Cards/Inner

Four Pack

S4724 4 Watt Clear
S4725 7 Watt Clear
S4726 7 Watt White

Packing: 4 Bulbs/Card
 48 Cards/Master,
 12 Cards/Inner

Not Shown
Actual Size



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./Inner Pack |
|-------|-----------|-------|-----------------|-----------|---------|-------|------------------|--------|----------|--------|------------|----------------------|
| 4 | C7 | Cand. | S3797 | 4C7 | Clear | 120V | 3000 | 16 | C-7A | 2 1/8" | Card/2 | 400/20 |
| 4 | C7 | Cand. | S4724 | 4C7 | Clear | 120V | 3000 | 16 | C-7A | 2 1/8" | Card/4 | 48/12 |
| 7 | C7 | Cand. | S3791 | 7C7 | Clear | 120V | 3000 | 35 | C-7A | 2 1/8" | Card/2 | 400/20 |
| 7 | C7 | Cand. | S3792 | 7C7/W | White | 120V | 3000 | 20 | C-7A | 2 1/8" | Card/2 | 400/20 |
| 7 | C7 | Cand. | S4725 | 7C7 | Clear | 120V | 3000 | 35 | C-7A | 2 1/8" | Card/4 | 48/12 |
| 7 | C7 | Cand. | S4726 | 7C7/W | White | 120V | 3000 | 20 | C-7A | 2 1/8" | Card/4 | 48/12 |
| 40 | A15 | Med. | S3720 | 40A15 | Clear | 130V | 2500 | 290 | C-9 | 3 1/2" | Card/1 | 240/20 |
| 40 | A15 | Med. | S3721 | 40A15/F | Frosted | 130V | 2500 | 280 | C-9 | 3 1/2" | Card/1 | 240/20 |
| 60 | A15 | Med. | S3739 | 60A15 | Clear | 130V | 2500 | 580 | C-9 | 3 1/2" | Card/1 | 240/20 |
| 60 | A15 | Med. | S3740 | 60A15/F | Frosted | 130V | 2500 | 530 | C-9 | 3 1/2" | Card/1 | 240/20 |

Carded lamps

Specialty Bulbs



Carded

2500 Hours / 130 Volt

Clear Appliance, Indicator, Switchboard & Night Light



Indicator Bulb

S4722 15 Watt
Int. Base/130 Volt
Dom. Code #15T7/N



Appliance Bulb

S4718 15 Watt
Cand. Base/130 Volt
Dom. Code #15T7C



Indicator Bulb

S4719 15 Watt
D.C. Bay. Base/130 Volt
Dom. Code #15T7/DC



Appliance Bulb

S4720 25 Watt
Int. Base/130 Volt
Dom. Code #25T8N



Indicator Bulb

S4721 25 Watt
D.C. Bay. Base/130 Volt
Dom. Code #25T8DC



**Microwave
Oven Bulb**
S3917 40 Watt
Int. Base/130 Volt
Dom. Code #40T8N



Indicator Bulb
S4717 6 Watt
Cand. Base/130 Volt
Dom. Code #6S6

Packing:
2 Bulb/Card
120 Cards/Master,
12 Cards/Inner

Packing:
1 Bulb/Card
120 Cards/Master,
12 Cards/Inner

Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 6 | S6 | Cand. | S4717 | 6S6 | Clear | 130V | 2500 | 30 | C-7A | 1 7/8" | Card/2 | 120/12 |
| 15 | T7 | Cand. | S4718 | 15T7/C | Clear | 130V | 2500 | 95 | C-5A | 2 1/4" | Card/1 | 120/12 |
| 15 | T7 | Int. | S4722 | 15T7/N | Clear | 130V | 2500 | 95 | C-5A | 2 1/4" | Card/1 | 120/12 |
| 15 | T7 | DC Bayonet | S4719 | 15T7/DC | Clear | 130V | 2500 | 95 | C-5A | 2 1/4" | Card/1 | 120/12 |
| 25 | T8 | Int. | S4720 | 25T8/N | Clear | 130V | 2500 | 190 | C-5A | 2 5/8" | Card/1 | 120/12 |
| 25 | T8 | DC Bayonet | S4721 | 25T8/DC | Clear | 130V | 2500 | 190 | C-5A | 2 5/8" | Card/1 | 120/12 |
| 40 | T8 | Int. | S3917 | 40T8N | Clear | 130V | 2500 | 370 | CC-2V | 2 5/8" | Card/1 | 120/12 |

carded lamps

Carded R14 & R16

1500 Hours



R14

Medium Base
120 Volt

S4704 25 Watt
S4705 40 Watt

Packing: 1 Bulb/Card
120 Cards/Master,
10 Cards/Inner



R14

Intermediate Base
120 Volt

S4700 25 Watt
S4701 40 Watt

Packing: 1 Bulb/Card
120 Cards/Master,
10 Cards/Inner



R16

Medium Base
120 Volt

S4702 40 Watt

Packing: 1 Bulb/Card
120 Cards/Master,
10 Cards/Inner



R14

Euro. (Mignon) Base
130 Volt

S4706 40 Watt

Packing: 1 Bulb/Card
120 Cards/Master,
10 Cards/Inner

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|-----------|-------|------------------|--------|----------|---------|------------|-----------------------|
| 25 | R14 | Int. | S4700 | 25R14N | Lt. Frost | 120V | 1500 | 135 | CC2V | 2 5/8" | Card/1 | 120/10 |
| 25 | R14 | Med. | S4704 | 25R14 | Lt. Frost | 120V | 1500 | 135 | CC2V | 2 5/8" | Card/1 | 120/10 |
| 40 | R14 | Euro | S4706 | 40R14 | Lt. Frost | 130V | 1500 | 280 | CC2V | 2 5/8" | Card/1 | 120/10 |
| 40 | R14 | Int. | S4701 | 40R14N | Lt. Frost | 120V | 1500 | 280 | CC2V | 2 5/8" | Card/1 | 120/10 |
| 40 | R14 | Med. | S4705 | 40R14 | Lt. Frost | 120V | 1500 | 280 | CC2V | 2 5/8" | Card/1 | 120/10 |
| 40 | R16 | Med. | S4702 | 40R16 | Frost | 120V | 1500 | 280 | C-9 | 3 7/16" | Card/1 | 120/10 |

Carded lamps



Halogen MR11 & MR16



Carded Lamps

UV all carded
PROTECTED halogen
NO HARMFUL items feature
ULTRAVIOLET UV protection
RAY S

2000 Hours

carded lamps



MR11

12 Volt Bi-Pin Base
 JRM Type

Promotional
 2/Pack

- S3464** 20 Watt SP FTC
- S3465** 20 Watt NFL FTD
- S3466** 35 Watt SP FTF
- S3467** 35 Watt NFL FTH

- S3424** 20 Watt NFL FTD
- S3425** 35 Watt NFL FTH

Packing:
 1 Bulb/Card
 12 Cards/Master,

Packing:
 2 Bulbs/Card
 12 Cards/Master



MR16

12 Volt Bi-Pin Base
 JR Type

- S3460** 20 Watt SP ESX
- S3461** 20 Watt FL BAB
- S3462** 50 Watt SP EXT
- S3463** 50 Watt FL EXN

Packing:
 1 Bulb/Card
 12 Cards/Master,

Not Shown Actual Size


| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|---------|-------|------------------|-------|----------|--------|------------|-----------------------|
| 20 | MR11 | GZ4 | S3464 | 20MR11 FTC | SP 12° | 12V | 2000 | 1750 | C-6 | 1 1/4" | Card/1 | 12 |
| 20 | MR11 | GZ4 | S3465 | 20MR11 FTD | NFL 24° | 12V | 2000 | 700 | C-6 | 1 1/4" | Card/1 | 12 |
| 20 | MR11 | GZ4 | S3424 | 20MR11 FTD | NFL 24° | 12V | 2000 | 700 | C-6 | 1 1/4" | Card/2 | 12 |
| 35 | MR11 | GZ4 | S3466 | 35MR11 FTF | SP 12° | 12V | 2000 | 2500 | C-6 | 1 1/4" | Card/1 | 12 |
| 35 | MR11 | GZ4 | S3467 | 35MR11 FTH | NFL 24° | 12V | 2000 | 1550 | C-6 | 1 1/4" | Card/1 | 12 |
| 35 | MR11 | GZ4 | S3425 | 35MR11 FTH | NFL 24° | 12V | 2000 | 1550 | C-6 | 1 1/4" | Card/2 | 12 |
| 20 | MR16 | GX5.3 | S3460 | 20MR11 ESX | NSP 9° | 12V | 2000 | 4100 | C-8 | 1 7/8" | Card/1 | 12 |
| 20 | MR16 | GX5.3 | S3461 | 20MR11 BAB | FL 36° | 12V | 2000 | 700 | C-6 | 1 7/8" | Card/1 | 12 |
| 50 | MR16 | GX5.3 | S3462 | 50MR11 EXT | NSP 9° | 12V | 2000 | 10000 | C-6 | 1 7/8" | Card/1 | 12 |
| 50 | MR16 | GX5.3 | S3463 | 50MR11 EXN | FL 36° | 12V | 2000 | 1700 | C-8 | 1 7/8" | Card/1 | 12 |

2000 Hours

all carded
halogen
items feature
UV protection



Carded Lamps



BA15D

Double Contact

- S3432** 75 Watt
- S3488** 100 Watt
- S3489** 150 Watt
- S3490** 250 Watt

Packing:
1 Bulb/Card
12 Cards/Master



E14

European Base

- S3491** 100 Watt
- S3492** 150 Watt
- S3493** 250 Watt

Packing:
1 Bulb/Card
12 Cards/Master



E11

Mini Can

- S3484** 75 Watt
- S3485** 100 Watt
- S3486** 150 Watt
- S3487** 250 Watt

Packing:
1 Bulb/Card
12 Cards/Master



Carded Lamps

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|--------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 75 | T4 | E11 | S3484 | 75Q/CL | Clear | 120V | 2000 | 1250 | CC-8 | 2 11/16" | Card/1 | 12 |
| 75 | T4 | DC Bay | S3432 | 75Q/CL | Clear | 120V | 2000 | 1250 | CC-8 | 2 13/32" | Card/1 | 12 |
| 100 | T4 | E11 | S3485 | 100Q/CL | Clear | 120V | 2000 | 1600 | CC-8 | 2 11/16" | Card/1 | 12 |
| 100 | T4 | DC Bay | S3488 | 100Q/CL | Clear | 120V | 2000 | 1600 | CC-8 | 2 13/32" | Card/1 | 12 |
| 100 | T4 | E14 | S3491 | 100Q/CL | Clear | 120V | 2000 | 1600 | CC-8 | 2 15/16" | Card/1 | 12 |
| 150 | T4 | E11 | S3486 | 150Q/CL | Clear | 120V | 2000 | 2400 | CC-8 | 2 23/32" | Card/1 | 12 |
| 150 | T4 | DC Bay | S3489 | 150Q/CL | Clear | 120V | 2000 | 2400 | CC-8 | 2 13/32" | Card/1 | 12 |
| 150 | T4 | E14 | S3492 | 150Q/CL | Clear | 120V | 2000 | 2400 | CC-8 | 3 1/32" | Card/1 | 12 |
| 250 | T4.5 | E11 | S3487 | 250Q/CL | Clear | 120V | 2000 | 4350 | CC-8 | 3 5/32" | Card/1 | 12 |
| 250 | T4.5 | DC Bay | S3490 | 250Q/CL | Clear | 120V | 2000 | 4350 | CC-8 | 2 27/32" | Card/1 | 12 |
| 250 | T4.5 | E14 | S3493 | 250Q/CL | Clear | 120V | 2000 | 4350 | CC-8 | 3 11/32" | Card/1 | 12 |



Halogen



Carded Lamps



all carded halogen items feature UV protection

2000 Hours

12 Volt

Promotional
2/Pack

S3420 20 Watt

S3421 50 Watt

Packing: 2 Bulbs/Card
12 Cards/Master



12 Volt

S3459 10 Watt

S3468 20 Watt

S3469 35 Watt

S3470 50 Watt

S3471 75 Watt

Packing: 1 Bulb/Card
12 Cards/Master



120 Volt

G8 Base

S3540 35 Watt

S3541 50 Watt

S3542 75 Watt

S3543 100 Watt

120 Volt

G9 Base

S3544 35 Watt

S3545 50 Watt

S3546 75 Watt

S3547 100 Watt

Packing: 1 Bulb/Card
12 Cards/Master



G8 Base

G9 Base

GY6.35 Base

120 Volt

GY6.35 Base

S3418 35 Watt

S3427 50 Watt

S3428 75 Watt

S3419 100 Watt

Packing: 1 Bulb/Card
12 Cards/Master

Not Shown
Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Carton |
|-------|-----------|--------|-----------------|-----------|--------|-------|------------------|--------|----------|--------|------------|--------|
| 10 | T3 | G4 | S3459 | 10T3 | Clear | 12V | 2000 | 120 | C-6 | 32mm | Card/1 | 12 |
| 20 | T3 | G4 | S3468 | 20T3 | Clear | 12V | 2000 | 320 | C-6 | 32mm | Card/1 | 12 |
| 20 | T3 | G4 | S3420 | 20T3 | Clear | 12V | 2000 | 320 | C-6 | 32mm | Card/2 | 12 |
| 35 | T4 | GY6.35 | S3469 | 35T4 | Clear | 12V | 2000 | 600 | C-6 | 41mm | Card/1 | 12 |
| 35 | T4 | GY6.35 | S3418 | 35T4 | Clear | 120V | 2000 | 400 | C-6 | 50mm | Card/1 | 12 |
| 35 | T4 | G8 | S3540 | 35T4 | Clear | 120V | 2000 | 400 | C-6 | 46mm | Card/1 | 12 |
| 35 | T4 | G9 | S3544 | 35T4 | Clear | 120V | 2000 | 400 | C-6 | 45mm | Card/1 | 12 |
| 50 | T4 | GY6.35 | S3470 | 50T4 | Clear | 12V | 2000 | 900 | C-6 | 41mm | Card/1 | 12 |
| 50 | T4 | GY6.35 | S3421 | 50T4 | Clear | 12V | 2000 | 900 | C-6 | 41mm | Card/2 | 12 |
| 50 | T4 | GY6.35 | S3427 | 50T4 | Clear | 120V | 2000 | 750 | CC-8 | 50mm | Card/1 | 12 |
| 50 | T4 | G8 | S3541 | 50T4 | Clear | 120V | 2000 | 750 | CC-8 | 46mm | Card/1 | 12 |
| 50 | T4 | G9 | S3545 | 50T4 | Clear | 120V | 2000 | 750 | CC-8 | 45mm | Card/1 | 12 |
| 75 | T4 | GY6.35 | S3471 | 75T4 | Clear | 12V | 2000 | 1350 | C-6 | 41mm | Card/1 | 12 |
| 75 | T4 | GY6.35 | S3428 | 75T4 | Clear | 120V | 2000 | 1250 | CC-8 | 60mm | Card/1 | 12 |
| 75 | T4 | G8 | S3542 | 75T4 | Clear | 120V | 2000 | 1250 | CC-8 | 58mm | Card/1 | 12 |
| 75 | T4 | G9 | S3546 | 75T4 | Clear | 120V | 2000 | 1250 | CC-8 | 56mm | Card/1 | 12 |
| 100 | T4 | GY6.35 | S3419 | 100T4 | Clear | 120V | 2000 | 1600 | CC-8 | 60mm | Card/1 | 12 |
| 100 | T4 | G8 | S3543 | 100T4 | Clear | 120V | 2000 | 1600 | CC-8 | 58mm | Card/1 | 12 |
| 100 | T4 | G9 | S3547 | 100T4 | Clear | 120V | 2000 | 1600 | CC-8 | 56mm | Card/1 | 12 |


carded lamps

2000 Hours

all carded
halogen
items feature
UV protection



Carded Lamps



JDR Lensed

**Medium
Screw Base**

- S3438** 75W Flood
- S3439** 100W Flood

**Intermediate
Screw Base**

- S3434** 75W Flood
- S3435** 100W Flood

Packing: 1 Bulb/Card
12 Cards/Master



Double -

JDD Envelope

Medium Base 120 Volt

- S3472** 75 Watt Clear
- S3473** 100 Watt Clear
- S3474** 150 Watt Clear
- S3475** 250 Watt Clear
- S3476** 75 Watt Frosted
- S3477** 100 Watt Frosted
- S3478** 150 Watt Frosted
- S3479** 250 Watt Frosted

Packing: 1 Bulb/Card
12 Cards/Master

**MR16 Twist Base
GU10 Base 120 Volt**

- S3500** 20 Watt
- S3501** 35 Watt
- S3502** 50 Watt

Packing: 12 Cards/Inner
120 Cards/Master



Not Shown Actual Size

Carded Lamps

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Carton |
|-------|-----------|------|-----------------|--------------|---------|-------|------------------|--------|----------|--------|------------|--------|
| 20 | JCDR | GU10 | S3500 | 20GU10/CL | Clear | 120V | 2000 | 1050 | CC-8 | 1 7/8" | Card/1 | 12 |
| 35 | JCDR | GU10 | S3501 | 35GU10/CL | Clear | 120V | 2000 | 1000 | CC-8 | 1 7/8" | Card/1 | 12 |
| 50 | JCDR | GU10 | S3502 | 50GU10/CL | Clear | 120V | 2000 | 1650 | CC-8 | 1 7/8" | Card/1 | 12 |
| 75 | T10 | Med. | S3472 | 75T10Q/CL | Clear | 120V | 2000 | 1050 | CC-8 | 4" | Card/1 | 12 |
| 75 | T10 | Med. | S3476 | 75T10Q/F | Frosted | 120V | 2000 | 1000 | CC-8 | 4" | Card/1 | 12 |
| 75 | JDR | INT. | S3434 | 75JDR/N/EXN | Clear | 120V | 2000 | 1650 | CC-8 | 2 7/8" | Card/1 | 12 |
| 75 | JDR | MED. | S3438 | 75JDR/EXN | Clear | 120V | 2000 | 1650 | CC-8 | 2 7/8" | Card/1 | 12 |
| 100 | JDR | INT. | S3435 | 100JDR/N/EXN | Clear | 120V | 2000 | 1950 | CC-8 | 2 7/8" | Card/1 | 12 |
| 100 | JDR | MED. | S3439 | 100JDR/EXN | Clear | 120V | 2000 | 1950 | CC-8 | 2 7/8" | Card/1 | 12 |
| 100 | T10 | Med. | S3473 | 100T10Q/CL | Clear | 120V | 2000 | 1500 | CC-8 | 4" | Card/1 | 12 |
| 100 | T10 | Med. | S3477 | 100T10Q/F | Frosted | 120V | 2000 | 1420 | CC-8 | 4" | Card/1 | 12 |
| 150 | T10 | Med. | S3474 | 150T10Q/CL | Clear | 120V | 2000 | 2500 | CC-8 | 4" | Card/1 | 12 |
| 150 | T10 | Med. | S3478 | 150T10Q/F | Frosted | 120V | 2000 | 2300 | CC-8 | 4" | Card/1 | 12 |
| 250 | T10 | Med. | S3475 | 250T10Q/CL | Clear | 120V | 2000 | 4200 | CC-8 | 4" | Card/1 | 12 |
| 250 | T10 | Med. | S3479 | 250T10Q/F | Frosted | 120V | 2000 | 3900 | CC-8 | 4" | Card/1 | 12 |

Halogen *Double Ended* Carded Lamps



all carded
halogen
items feature
UV protection

2000 Hours



78MM J-Type (Short) 120V

- S3480** 100 Watt
- S3481** 150 Watt
- S3482** 200 Watt
- S3426** 250 Watt

Packing:
1 Bulb/Card
12 Cards/Master



118MM J-Type (Long) 120V

- S3431** 100 Watt
- S3494** 150 Watt
- S3495** 200 Watt
- S3496** 300 Watt

S3497 500 Watt
Packing:
1 Bulb/Card
12 Cards/Master



Flat Blade

145MM J-Type (Blade) 120V

- S3429** 300 Watt

Packing: 1 Bulb/Card
12 Cards/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 100 | T3 | RS7 | S3480 | 100T3Q/CL | Clear | 120V | 2000 | 1650 | C-8 | 3 1/8" | Card/1 | 12 |
| 150 | T3 | RS7 | S3481 | 150T3Q/CL | Clear | 120V | 2000 | 2600 | C-8 | 3 1/8" | Card/1 | 12 |
| 200 | T3 | RS7 | S3482 | 200T3Q/CL | Clear | 120V | 2000 | 3200 | C-8 | 3 1/8" | Card/1 | 12 |
| 250 | T3 | RS7 | S3426 | 250T3Q/CL | Clear | 120V | 2000 | 3950 | C-8 | 3 1/8" | Card/1 | 12 |
| 100 | T3 | RS7 | S3431 | 100T3Q/CL | Clear | 120V | 2000 | 1650 | C-8 | 4 11/16" | Card/1 | 12 |
| 150 | T3 | RS7 | S3494 | 150T3Q/CL | Clear | 120V | 2000 | 2600 | C-8 | 4 11/16" | Card/1 | 12 |
| 200 | T3 | RS7 | S3495 | 200T3Q/CL | Clear | 120V | 2000 | 3200 | C-8 | 4 11/16" | Card/1 | 12 |
| 300 | T3 | RS7 | S3496 | 300T3Q/CL | Clear | 120V | 2000 | 5000 | C-8 | 4 11/16" | Card/1 | 12 |
| 500 | T3 | RS7 | S3497 | 500T3Q/CL | Clear | 120V | 2000 | 9500 | C-8 | 4 11/16" | Card/1 | 12 |
| 300 | T3 | Blade | S3429 | 300T3Q/CL | Clear | 120V | 2000 | 5000 | C-8 | 5 13/16" | Card/1 | 12 |

carded lamps



Halogen *Double Ended* *Carded* Lamps

2000 Hours

all carded halogen items feature UV protection




Promotional Packs



78MM J-Type Short (120V) 2 Pack

- S3422 100 Watt
- S3423 150 Watt

Packing:
2 Bulbs/Card
12 Cards/Master



118MM J-Type Long (120V) 2 Pack

- S3430 300 Watt
- S3433 500 Watt

Packing:
2 Bulbs/Card
12 Cards/Master



118MM J-Type Long (120V) 3 Pack

- S3410 300 Watt
- S3411 500 Watt

Packing:
3 Bulbs/Card
12 Cards/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|-----------|--------|-------|------------------|--------|----------|----------|------------|-----------------------|
| 100 | T3 | RS7 | S3422 | 100T3Q/CL | Clear | 120V | 2000 | 1650 | C-8 | 3 1/8" | Card/2 | 12 |
| 150 | T3 | RS7 | S3423 | 150T3Q/CL | Clear | 120V | 2000 | 2600 | C-8 | 3 1/8" | Card/2 | 12 |
| 300 | T3 | RS7 | S3430 | 300T3Q/CL | Clear | 120V | 2000 | 3200 | C-8 | 4 11/16" | Card/2 | 12 |
| 300 | T3 | RS7 | S3410 | 300T3Q/CL | Clear | 120V | 2000 | 3200 | C-8 | 4 11/16" | Card/3 | 12 |
| 500 | T3 | RS7 | S3433 | 500T3Q/CL | Clear | 120V | 2000 | 9500 | C-8 | 4 11/16" | Card/2 | 12 |
| 500 | T3 | RS7 | S3411 | 500T3Q/CL | Clear | 120V | 2000 | 9500 | C-8 | 4 11/16" | Card/3 | 12 |

Carded lamps

Compact Fluorescent Lamps



10,000 Hours



Quad Tube



Twin Tube

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Pack. Type | Mst.Ctn./ InnerPack |
|---------------------------|-----------|--------|-----------------|------------|-------------|------------------|--------|--------|------------|---------------------|
| Two Pin Twin Tubes | | | | | | | | | | |
| 5 | T4 | G23 | S6300 | CFS5W/827 | 2700K 82CRI | 10000 | 230 | 4.2" | Box | 50/5 |
| 7 | T4 | G23 | S6302 | CFS7W/827 | 2700K 82CRI | 10000 | 400 | 5.3" | Box | 50/5 |
| 9 | T4 | G23 | S6306 | CFS9W/827 | 2700K 82CRI | 10000 | 580 | 6.5" | Box | 50/5 |
| 13 | T4 | GX23 | S6310 | CFS13W/827 | 2700K 82CRI | 10000 | 800 | 7.1" | Box | 50/5 |
| Two Pin Quad Tubes | | | | | | | | | | |
| 9 | T4 | G23-2 | S6314 | CFD9W/827 | 2700K 82CRI | 10000 | 525 | 4.3" | Box | 50/5 |
| 13 | T4 | GX23-2 | S6317 | CFD13W/827 | 2700K 82CRI | 10000 | 780 | 4.6" | Box | 50/5 |
| 18 | T4 | G24D-2 | S6321 | CFD18W/827 | 2700K 82CRI | 10000 | 1250 | 6.0" | Box | 50/5 |
| 26 | T4 | G24D-3 | S6325 | CFD26W/827 | 2700K 82CRI | 10000 | 1825 | 6.8" | Box | 50/5 |

For full selection see *Compact Fluorescent* section of catalog

carded lamps

Fluorescent Sub-Miniature T2 Tubes

Not Shown Actual Size



FM6

FM8

FM11

FM13

6 Watt

Axial Base

S6488 3000K

S2900 3500K

S6489 4100K

Packing:

20/Master

8 Watt

Axial Base

S6490 3000K

S2901 3500K

S6491 4100K

Packing:

20/Master

11 Watt

Axial Base

S6492 3000K

S2902 3500K

S6493 4100K

Packing:

20/Master

13 Watt

Axial Base

S6494 3000K

S2903 3500K

S6495 4100K

Packing:

20/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Kelvin | CRI | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------|-----------------|-----------|--------|-----|------------------|----------------|----------------|--------|
| 6 | T2 | Axial | S6488 | FM6/830 | 3000 | 80 | 10,000 | 330 | 8.6" | 20 |
| 6 | T2 | Axial | S2900 | FM6/835 | 3500 | 80 | 10,000 | 330 | 8.6" | 20 |
| 6 | T2 | Axial | S6489 | FM6/841 | 4100 | 80 | 10,000 | 330 | 8.6" | 20 |
| 8 | T2 | Axial | S6490 | FM8/830 | 3000 | 80 | 10,000 | 540 | 12.6" | 20 |
| 8 | T2 | Axial | S2901 | FM8/835 | 3500 | 80 | 10,000 | 540 | 12.6" | 20 |
| 8 | T2 | Axial | S6491 | FM8/841 | 4100 | 80 | 10,000 | 540 | 12.6" | 20 |
| 11 | T2 | Axial | S6492 | FM11/830 | 3000 | 80 | 10,000 | 750 | 16.6" | 20 |
| 11 | T2 | Axial | S2902 | FM11/835 | 3500 | 80 | 10,000 | 750 | 16.6" | 20 |
| 11 | T2 | Axial | S6493 | FM11/841 | 4100 | 80 | 10,000 | 750 | 16.6" | 20 |
| 13 | T2 | Axial | S6494 | FM13/830 | 3000 | 80 | 10,000 | 930 | 20.6" | 20 |
| 13 | T2 | Axial | S2903 | FM13/835 | 3500 | 80 | 10,000 | 930 | 20.6" | 20 |
| 13 | T2 | Axial | S6495 | FM13/841 | 4100 | 80 | 10,000 | 930 | 20.6" | 20 |

Fluorescent High Performance T5 Tubes



Not Shown Actual Size

Tri-Phosphor — Electronic Ballast

Standard Mini Bi Pin Base

14W

S6425 3000K
S6426 3500K
S6427 4100K

21W

S6428 3000K
S6429 3500K
S6430 4100K

28W

S6431 3000K
S6432 3500K
S6433 4100K

35W

S6434 3000K
S6435 3500K
S6436 4100K

40/Master



High Output Mini Bi Pin Base

24W

S6437 3000K
S6438 3500K
S6439 4100K

39W

S6440 3000K
S6441 3500K
S6442 4100K

54W

S6443 3000K
S6444 3500K
S6445 4100K

80W

S6446 3000K
S6447 3500K
S6448 4100K

40/Master

Standard

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Kelvin | CRI | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------------|-----------------|-----------|--------|-----|------------------|----------------|----------------|--------|
| 14 | T5 | Mini Bi Pin | S6425 | FP14/830 | 3000 | 82 | 20,000 | 1275 | 24" | 40 |
| 14 | T5 | Mini Bi Pin | S6426 | FP14/835 | 3500 | 82 | 20,000 | 1275 | 24" | 40 |
| 14 | T5 | Mini Bi Pin | S6427 | FP14/841 | 4100 | 82 | 20,000 | 1275 | 24" | 40 |
| 21 | T5 | Mini Bi Pin | S6428 | FP21/830 | 3000 | 82 | 20,000 | 2000 | 36" | 40 |
| 21 | T5 | Mini Bi Pin | S6429 | FP21/835 | 3500 | 82 | 20,000 | 2000 | 36" | 40 |
| 21 | T5 | Mini Bi Pin | S6430 | FP21/841 | 4100 | 82 | 20,000 | 2000 | 36" | 40 |
| 28 | T5 | Mini Bi Pin | S6431 | FP28/830 | 3000 | 82 | 20,000 | 2750 | 48" | 40 |
| 28 | T5 | Mini Bi Pin | S6432 | FP28/835 | 3500 | 82 | 20,000 | 2750 | 48" | 40 |
| 28 | T5 | Mini Bi Pin | S6433 | FP28/841 | 4100 | 82 | 20,000 | 2750 | 48" | 40 |
| 35 | T5 | Mini Bi Pin | S6434 | FP35/830 | 3000 | 82 | 20,000 | 3425 | 60" | 40 |
| 35 | T5 | Mini Bi Pin | S6435 | FP35/835 | 3500 | 82 | 20,000 | 3425 | 60" | 40 |
| 35 | T5 | Mini Bi Pin | S6436 | FP35/841 | 4100 | 82 | 20,000 | 3425 | 60" | 40 |

High Output

| | | | | | | | | | | |
|----|----|-------------|-------|-------------|------|----|--------|------|-----|----|
| 24 | T5 | Mini Bi Pin | S6437 | FP24/830/HO | 3000 | 82 | 20,000 | 1875 | 24" | 40 |
| 24 | T5 | Mini Bi Pin | S6438 | FP24/835/HO | 3500 | 82 | 20,000 | 1875 | 24" | 40 |
| 24 | T5 | Mini Bi Pin | S6439 | FP24/841/HO | 4100 | 82 | 20,000 | 1875 | 24" | 40 |
| 39 | T5 | Mini Bi Pin | S6440 | FP39/830/HO | 3000 | 82 | 20,000 | 3300 | 36" | 40 |
| 39 | T5 | Mini Bi Pin | S6441 | FP39/835/HO | 3500 | 82 | 20,000 | 3300 | 36" | 40 |
| 39 | T5 | Mini Bi Pin | S6442 | FP39/841/HO | 4100 | 82 | 20,000 | 3300 | 36" | 40 |
| 54 | T5 | Mini Bi Pin | S6443 | FP54/830/HO | 3000 | 82 | 20,000 | 4725 | 48" | 40 |
| 54 | T5 | Mini Bi Pin | S6444 | FP54/835/HO | 3500 | 82 | 20,000 | 4725 | 48" | 40 |
| 54 | T5 | Mini Bi Pin | S6445 | FP54/841/HO | 4100 | 82 | 20,000 | 4725 | 48" | 40 |
| 80 | T5 | Mini Bi Pin | S6446 | FP80/830/HO | 3000 | 82 | 20,000 | 6575 | 60" | 40 |
| 80 | T5 | Mini Bi Pin | S6447 | FP80/835/HO | 3500 | 82 | 20,000 | 6575 | 60" | 40 |
| 80 | T5 | Mini Bi Pin | S6448 | FP80/841/HO | 4100 | 82 | 20,000 | 6575 | 60" | 40 |

fluorescent lamps

Fluorescent T5 Tubes Preheat



5000 Hours

Not Shown Actual Size



Blacklights

F4T5

F6T5

F8T5

F13T5

Blacklight

- S2904 4 Watt
- S2905 6 Watt
- S2906 8 Watt

Blacklight Blue

- S6405 4 Watt
- S2907 6 Watt
- S6406 8 Watt

Packing: 24/Master,
Individually Boxed

4 Watt

- Mini Bi Pin Base
- S1900 Cool White
- S2908 Daylight

Packing: 20/Master,
Individually Boxed

6 Watt

- Mini Bi Pin Base
- S1902 Cool White
- S2909 Daylight

Packing: 20/Master,
Individually Boxed

8 Watt

- Mini Bi Pin Base
- S1904 Cool White
- S1905 Warm White
- S2910 Daylight

Packing: 20/Master,
Individually Boxed

13 Watt

- Mini Bi Pin Base
- S1906 Cool White
- S1907 Warm White
- S2911 Daylight

Packing: 20/Master,
Individually Boxed

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Pack. Type | Carton |
|-------|-----------|-------------|-----------------|-----------|-----------------|------------------|----------------|----------------|------------|--------|
| 4 | T5 | Mini Bi Pin | S1900 | F4T5/CW | Cool White | 5000 | 135 | 6" | Box | 20 |
| 4 | T5 | Mini Bi Pin | S2908 | F4T5/D | Daylight | 5000 | 115 | 6" | Box | 20 |
| 4 | T5 | Mini Bi Pin | S2904 | F4T5/BL | Blacklight | 5000 | n/a | 6" | Sleeve | 20 |
| 4 | T5 | Mini Bi Pin | S6405 | F4T5/BLB | Blacklight Blue | 5000 | n/a | 6" | Sleeve | 20 |
| 6 | T5 | Mini Bi Pin | S1902 | F6T5/CW | Cool White | 5000 | 270 | 9" | Box | 20 |
| 6 | T5 | Mini Bi Pin | S2909 | F6T5/D | Daylight | 5000 | 260 | 9" | Box | 20 |
| 6 | T5 | Mini Bi Pin | S2905 | F6T5/BL | Blacklight | 5000 | n/a | 9" | Sleeve | 20 |
| 6 | T5 | Mini Bi Pin | S2907 | F6T5/BLB | Blacklight Blue | 5000 | n/a | 9" | Sleeve | 20 |
| 8 | T5 | Mini Bi Pin | S1904 | F8T5/CW | Cool White | 5000 | 390 | 12" | Box | 20 |
| 8 | T5 | Mini Bi Pin | S2910 | F8T5/D | Daylight | 5000 | 350 | 12" | Box | 20 |
| 8 | T5 | Mini Bi Pin | S1905 | F8T5/WW | Warm White | 5000 | 400 | 12" | Box | 20 |
| 8 | T5 | Mini Bi Pin | S2906 | F8T5/BL | Blacklight | 5000 | n/a | 12" | Sleeve | 20 |
| 8 | T5 | Mini Bi Pin | S6406 | F8T5/BLB | Blacklight Blue | 5000 | n/a | 12" | Sleeve | 20 |
| 13 | T5 | Mini Bi Pin | S1906 | F13T5/CW | Cool White | 5000 | 860 | 21" | Box | 20 |
| 13 | T5 | Mini Bi Pin | S2911 | F13T5/D | Daylight | 5000 | 780 | 21" | Box | 20 |
| 13 | T5 | Mini Bi Pin | S1907 | F13T5/WW | Warm White | 5000 | 870 | 21" | Box | 20 |

fluorescent lamps

Fluorescent T8 Tubes Preheat

Not Shown Actual Size



F30T8

30 Watt 36"
Medium Bi Pin Base

- S6517** Cool White
- S6518** Daylight
- S6519** Warm White

Packing: 24/Master



F18T8

T8 Appliance
Medium Bi Pin Base

- S6513** Cool White/24"
- S6514** Cool White/26"
- S6515** Cool White/28"
- S6516** Cool White/30"

Packing: 24/Master



F15T8

15 Watt 18"
Medium Bi Pin Base

- S6510** Cool White
- S6511** Daylight
- S6512** Warm White
- S6665** Full Spectrum*

Packing: 24/Master
*6/Master



F15T8

15 Watt 18"
Medium Bi Pin Base

- S6407** Black Light Blue
- S2918** Black Light

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------------|-----------------|---------------|------------------|------------------|----------------|----------------|--------|
| 15 | T8 | Med. Bi Pin | S6510 | F15T8/CW | Cool White | 7500 | 850 | 18" | 24 |
| 15 | T8 | Med. Bi Pin | S6511 | F15T8/D | Daylight | 7500 | 750 | 18" | 24 |
| 15 | T8 | Med. Bi Pin | S6512 | F15T8/WW | Warm White | 7500 | 845 | 18" | 24 |
| 15 | T8 | Med. Bi Pin | S6665 | F15T8/SUN | Full Spectrum | 12000 | 600 | 18" | 6 |
| 15 | T8 | Med. Bi Pin | S2918 | F15T8/BL | Black Light | 7500 | n/a | 18" | 25 |
| 15 | T8 | Med. Bi Pin | S6407 | F15T8/BLB | Black Light Blue | 7500 | n/a | 18" | 20 |
| 18 | T8 | Med. Bi Pin | S6513 | F18T8/CW/K/24 | Cool White | 7500 | 1190 | 24" | 24 |
| 18 | T8 | Med. Bi Pin | S6514 | F18T8/CW/K/26 | Cool White | 7500 | 1240 | 26" | 24 |
| 18 | T8 | Med. Bi Pin | S6515 | F18T8/CW/K/28 | Cool White | 7500 | 1240 | 28" | 24 |
| 18 | T8 | Med. Bi Pin | S6516 | F18T8/CW/K/30 | Cool White | 7500 | 1300 | 30" | 24 |
| 30 | T8 | Med. Bi Pin | S6517 | F30T8/CW | Cool White | 7500 | 1380 | 36" | 24 |
| 30 | T8 | Med. Bi Pin | S6518 | F30T8/D | Daylight | 7500 | 2180 | 36" | 24 |
| 30 | T8 | Med. Bi Pin | S6519 | F30T8/WW | Warm White | 7500 | 2150 | 36" | 24 |

fluorescent lamps

T8 Electronic Tubes

20,000 Hours

ENVIRONMENTALLY FRIENDLY SATCO T8 ELECTRONIC

fluorescent lamps are designed to meet the Federal Toxicity Characteristic Leaching Procedure (TCLP) criteria for classification as non-hazardous waste in most states*.



- Designed to pass Federal TCLP test*.
- Energy efficient T8 lamp.
- Available in 3000K, 3500K, 4100K, 5000K & 6500K
- 20,000–hours average life time.
- 700 Series lamps equal: 75CRI Good Color Rendition
- 800 Series lamps equal: 80-82 CRI Superior Color Rendition

*Regulations may vary. Check your local and state regulations.

Not Shown Actual Size

700 SERIES

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------------|-----------------|---------------|-------------|------------------|----------------|----------------|--------|
| 32 | T8 | Med. Bi Pin | S6617 | F32T8/730/ENV | 3000K 75CRI | 20000 | 2800 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6618 | F32T8/735/ENV | 3500K 75CRI | 20000 | 2800 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6619 | F32T8/741/ENV | 4100K 75CRI | 20000 | 2800 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6694 | F32T8/750/ENV | 5000K 75CRI | 20000 | 2650 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6695 | F32T6/765/ENV | 6500K 75CRI | 20000 | 2700 | 48" | 30 |

800 SERIES

| | | | | | | | | | |
|----|----|-------------|-------|---------------|-------------|-------|------|-----|----|
| 32 | T8 | Med. Bi Pin | S6401 | F32T8/830/ENV | 3000K 82CRI | 20000 | 2950 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6402 | F32T8/835/ENV | 3500K 82CRI | 20000 | 2950 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6403 | F32T8/841/ENV | 4100K 82CRI | 20000 | 2950 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6404 | F32T8/850/ENV | 5000K 80CRI | 20000 | 2800 | 48" | 30 |

Eco Fluorescent T8 Electronic Tubes

Color Reference Guide:
 730/830 = 3000K Warm White
 735/835 = 3500K Neutral
 741/841 = 4100K Cool White
 750/850 = 5000K Daylight
 765/865 = 6500K Daylight

700 Series lamps equal: 75CRI*
 Good color rendition

800 Series lamps equal: 80-85CRI*
 Superior color rendition

(Color rendering index*)





F32T8

32 Watt 48"
Medium Bi Pin Base

F25T8

25 Watt 36"
Medium Bi Pin Base

F17T8

17 Watt 24"
Medium Bi Pin Base

Not Shown
Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Carton |
|-------|-----------|-------------|-----------------|----------------|-------------|------------------|--------|--------|--------|
| 17 | T8 | Med. Bi Pin | S6520 | FO17/730/ECO | 3000K 75CRI | 20000 | 1300 | 24" | 30 |
| 17 | T8 | Med. Bi Pin | S6523 | FO17/830/ECO | 3000K 82CRI | 20000 | 1350 | 24" | 30 |
| 17 | T8 | Med. Bi Pin | S6521 | FO17/735/ECO | 3500K 75CRI | 20000 | 1300 | 24" | 30 |
| 17 | T8 | Med. Bi Pin | S6524 | FO17/835/ECO | 3500K 82CRI | 20000 | 1350 | 24" | 30 |
| 17 | T8 | Med. Bi Pin | S6522 | FO17/741/ECO | 4100K 75CRI | 20000 | 1300 | 24" | 30 |
| 17 | T8 | Med. Bi Pin | S6525 | FO17/841/ECO | 4100K 82CRI | 20000 | 1350 | 24" | 30 |
| 17 | T8 | Med. Bi Pin | S2913 | F17T8/SUN | 6280K 95CRI | 14000 | 750 | 24" | 6 |
| 25 | T8 | Med. Bi Pin | S6526 | FO25/730/ECO | 3000K 75CRI | 20000 | 1950 | 36" | 30 |
| 25 | T8 | Med. Bi Pin | S6529 | FO25/830/ECO | 3000K 82CRI | 20000 | 2150 | 36" | 30 |
| 25 | T8 | Med. Bi Pin | S6527 | FO25/735/ECO | 3500K 75CRI | 20000 | 1950 | 36" | 30 |
| 25 | T8 | Med. Bi Pin | S6530 | FO25/835/ECO | 3500K 82CRI | 20000 | 2150 | 36" | 30 |
| 25 | T8 | Med. Bi Pin | S6528 | FO25/741/ECO | 4100K 75CRI | 20000 | 1950 | 36" | 30 |
| 25 | T8 | Med. Bi Pin | S6531 | FO25/841/ECO | 4100K 82CRI | 20000 | 2150 | 36" | 30 |
| 25 | T8 | Med. Bi Pin | S2914 | F25T8/SUN | 6280K 95CRI | 14000 | 1200 | 36" | 6 |
| 32 | T8 | Med. Bi Pin | S6532 | FO32/730/ECO | 3000K 75CRI | 20000 | 2800 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6535 | FO32/830/ECO | 3000K 82CRI | 20000 | 2950 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S2915 | FO32/830XP/ECO | 3000K 85CRI | 24000 | 3000 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6533 | FO32/735/ECO | 3500K 75CRI | 20000 | 2800 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6536 | FO32/835/ECO | 3500K 82CRI | 20000 | 2950 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S2916 | FO32/835XP/ECO | 3500K 85CRI | 24000 | 3000 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6534 | FO32/741/ECO | 4100K 75CRI | 20000 | 2800 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S6537 | FO32/841/ECO | 4100K 82CRI | 20000 | 2950 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S2917 | FO32/841XP/ECO | 4100K 85CRI | 24000 | 3000 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S2918 | FO32/750/ECO | 5000K 75CRI | 20000 | 2650 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S2919 | FO32/850/ECO | 5000K 80CRI | 20000 | 2800 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S2920 | FO32/850XP/ECO | 5000K 85CRI | 24000 | 3000 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S2921 | FO32/765/ECO | 6500K 75CRI | 20000 | 2700 | 48" | 30 |
| 32 | T8 | Med. Bi Pin | S2922 | F32T8/SUN | 6000K 85CRI | 20000 | 2900 | 48" | 12 |

fluorescent lamps

Fluorescent T8 Electronic Tubes

700 Series lamps equal: 75CRI*
Good color rendition

800 Series lamps equal: 82CRI*
Superior color rendition

(Color rendering index*)



FO40 5 ft.

40 Watt 60"
Medium Bi Pin Base

"700" Series
S6544 FO40/730
S6545 FO40/735
S6546 FO40/741

"800" Series
S6547 FO40/830
S6548 FO40/835
S6549 FO40/841

Packing: 30/Master



FO96 8 ft.

59 Watt 96"
Single Pin Base

"700" Series
S6538 FO96/730
S6539 FO96/735
S6540 FO96/741

"800" Series
S6541 FO96/830
S6542 FO96/835
S6543 FO96/841

Packing: 24/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------------|-----------------|-----------|-------------|------------------|----------------|----------------|--------|
| 40 | T8 | Med. Bi Pin | S6544 | FO40/730 | 3000K 75CRI | 20000 | 3500 | 60" | 30 |
| 40 | T8 | Med. Bi Pin | S6545 | FO40/735 | 3500K 75CRI | 20000 | 3500 | 60" | 30 |
| 40 | T8 | Med. Bi Pin | S6546 | FO40/741 | 4100K 75CRI | 20000 | 3500 | 60" | 30 |
| 40 | T8 | Med. Bi Pin | S6547 | FO40/830 | 3000K 82CRI | 20000 | 3650 | 60" | 30 |
| 40 | T8 | Med. Bi Pin | S6548 | FO40/835 | 3500K 82CRI | 20000 | 3650 | 60" | 30 |
| 40 | T8 | Med. Bi Pin | S6549 | FO40/841 | 4100K 82CRI | 20000 | 3650 | 60" | 30 |
| 59 | T8 | Single Pin | S6538 | FO96/730 | 3000K 75CRI | 15000 | 5700 | 96" | 24 |
| 59 | T8 | Single Pin | S6539 | FO96/735 | 3500K 75CRI | 15000 | 5700 | 96" | 24 |
| 59 | T8 | Single Pin | S6540 | FO96/741 | 4100K 75CRI | 15000 | 5700 | 96" | 24 |
| 59 | T8 | Single Pin | S6541 | FO96/830 | 3000K 82CRI | 15000 | 5900 | 96" | 24 |
| 59 | T8 | Single Pin | S6542 | FO96/835 | 3500K 82CRI | 15000 | 5900 | 96" | 24 |
| 59 | T8 | Single Pin | S6543 | FO96/841 | 4100K 82CRI | 15000 | 5900 | 96" | 24 |

Fluorescent

20,000 Hours **T8 Electronic** U Bend Tubes



700 Series lamps
equal: 75CRI*
Good color
rendition

800 Series lamps
equal: 82CRI*
Superior color
rendition

(Color rendering index*)

Color Reference Guide:

730/830 = 3000K Warm White

735/835 = 3500K Neutral

741/841 = 4100K Cool White



FBO31
1 5/8" Leg Spacing

31 Watt
Medium Bi Pin Base

"800" Series

S6550 FBO31/830

S6551 FBO31/835

S6552 FBO31/841

S2923 FBO31/750

Packing: 15/Master

Not Shown
Actual Size



FBO32/6
6" Leg Spacing

32 Watt
Medium Bi Pin Base

"700" Series

"800" Series

S6553 FBO32/730/6

S6556 FBO32/830/6

S6554 FBO32/735/6

S6557 FBO32/835/6

S6555 FBO32/741/6

S6558 FBO32/841/6

S2924 FBO32/750/6

Packing: 16/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Leg Spacing | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------------|-----------------|-------------|-------------|------------------|-------------|----------------|----------------|--------|
| 31 | T8 | Med. Bi Pin | S6550 | FBO31/830 | 3000K 82CRI | 20000 | 1 5/8" | 2725 | 22 1/2" | 15 |
| 31 | T8 | Med. Bi Pin | S6551 | FBO31/835 | 3500K 82CRI | 20000 | 1 5/8" | 2725 | 22 1/2" | 15 |
| 31 | T8 | Med. Bi Pin | S6552 | FBO31/841 | 4100K 82CRI | 20000 | 1 5/8" | 2725 | 22 1/2" | 15 |
| 31 | T8 | Med. Bi Pin | S2923 | FBO31/750 | 5000K 75CRI | 20000 | 1 5/8" | 2600 | 22 1/2" | 15 |
| 32 | T8 | Med. Bi Pin | S6553 | FBO32/730/6 | 3000K 75CRI | 20000 | 6" | 2750 | 22 1/2" | 16 |
| 32 | T8 | Med. Bi Pin | S6556 | FBO32/830/6 | 3000K 82CRI | 20000 | 6" | 2850 | 22 1/2" | 16 |
| 32 | T8 | Med. Bi Pin | S6554 | FBO32/735/6 | 3500K 75CRI | 20000 | 6" | 2750 | 22 1/2" | 16 |
| 32 | T8 | Med. Bi Pin | S6557 | FBO32/835/6 | 3500K 82CRI | 20000 | 6" | 2850 | 22 1/2" | 16 |
| 32 | T8 | Med. Bi Pin | S6555 | FBO32/741/6 | 4100K 75CRI | 20000 | 6" | 2750 | 22 1/2" | 16 |
| 32 | T8 | Med. Bi Pin | S6558 | FBO32/841/6 | 4100K 82CRI | 20000 | 6" | 2850 | 22 1/2" | 16 |
| 32 | T8 | Med. Bi Pin | S2924 | FBO32/750/6 | 5000K 75CRI | 20000 | 6" | 2625 | 22 1/2" | 16 |

fluorescent lamps

Fluorescent T12 Tubes Preheat

7500 Hours

fluorescent lamps



F14T12

14 Watt 15"
Medium Bi Pin Base
S6559 Cool White
S6560 Daylight
S6561 Warm White

Packing:
30/Master



F15T12

15 Watt 18"
Medium Bi Pin Base
S6562 Cool White
S6563 Daylight
S6564 Warm White

Packing:
30/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------------|-----------------|-----------|-------------|------------------|----------------|----------------|--------|
| 14 | T12 | Med. Bi Pin | S6559 | F14T12/CW | Cool White | 7500 | 650 | 15" | 30 |
| 14 | T12 | Med. Bi Pin | S6560 | F14T12/D | Daylight | 7500 | 590 | 15" | 30 |
| 14 | T12 | Med. Bi Pin | S6561 | F14T12/WW | Warm White | 7500 | 660 | 15" | 30 |
| 15 | T12 | Med. Bi Pin | S6562 | F15T12/CW | Cool White | 7500 | 750 | 18" | 30 |
| 15 | T12 | Med. Bi Pin | S6563 | F15T12/D | Daylight | 7500 | 660 | 18" | 30 |
| 15 | T12 | Med. Bi Pin | S6564 | F15T12/WW | Warm White | 7500 | 770 | 18" | 30 |

Fluorescent T12 Tubes

Not Shown Actual Size



F30T12

30 Watt 36"
Rapid Start
Medium Bi Pin Base
S6571 Cool White
S6572 Day Light
S6573 Warm White
S6574 F30T12/D830
S6575 F30T12/D35
S6576 F30T12/D41
S6667 Full Spectrum*
Packing: 30/Master
*6/Master



F25T12

25 Watt
Preheat
Appliance
Medium Bi Pin Base
S6568 Cool White/28"
S6569 Cool White/30"
S6570 Cool White/33"
Packing: 30/Master



F20T12

20 Watt 24"
Preheat
General Purpose
Medium Bi Pin Base
S6565 Cool White
S6566 Daylight
S6567 Warm White
S6666 Full Spectrum*
Packing: 30/Master
6/Master*



**F20T12/F40T12
Blacklights**

20 Watt T12 24"
Preheat
Medium Bi Pin Base
S6408 Blacklight Blue
S2925 Blacklight

40 Watt T12 48"
Rapid Start
Medium Bi Pin Base
S6409 Blacklight Blue*
S2926 Blacklight
Packing: 30/Master
*6/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------------|-----------------|----------------|-----------------|------------------|----------------|----------------|--------|
| 20 | T12 | Med. Bi Pin | S6565 | F20T12/CW | Cool White | 9000 | 1220 | 24" | 30 |
| 20 | T12 | Med. Bi Pin | S6566 | F20T12/D | Daylight | 9000 | 1075 | 24" | 30 |
| 20 | T12 | Med. Bi Pin | S6567 | F20T12/WW | Warm White | 9000 | 1250 | 24" | 30 |
| 20 | T12 | Med. Bi Pin | S6666 | F20T12/SUN | Full Spectrum | 14000 | 800 | 24" | 6 |
| 20 | T12 | Med. Bi Pin | S6408 | F20T12/BLB | Blacklight Blue | 9000 | n/a | 24" | 30 |
| 20 | T12 | Med. Bi Pin | S2925 | F20T12/BL | Blacklight | 9000 | n/a | 24" | 30 |
| 25 | T12 | Med. Bi Pin | S6568 | F25T12/CW/28" | Cool White | 7500 | 1670 | 28" | 30 |
| 25 | T12 | Med. Bi Pin | S6569 | F25T12/CW/30" | Cool White | 7500 | 1730 | 30" | 30 |
| 25 | T12 | Med. Bi Pin | S6570 | F25T12/CW/33" | Cool White | 7500 | 1750 | 33" | 30 |
| 30 | T12 | Med. Bi Pin | S6571 | F30T12/CW/RS | Cool White | 18000 | 2200 | 36" | 30 |
| 30 | T12 | Med. Bi Pin | S6572 | F30T12/D/RS | Daylight | 18000 | 1900 | 36" | 30 |
| 30 | T12 | Med. Bi Pin | S6573 | F30T12/WW/RS | Warm White | 18500 | 2275 | 36" | 30 |
| 30 | T12 | Med. Bi Pin | S6574 | F30T12/D830/RS | 3000K 80CRI | 18000 | 2290 | 36" | 30 |
| 30 | T12 | Med. Bi Pin | S6575 | F30T12/D35/RS | 3500K 70CRI | 18000 | 2250 | 36" | 30 |
| 30 | T12 | Med. Bi Pin | S6576 | F30T12/D41/RS | 4100K 70CRI | 18000 | 2250 | 36" | 30 |
| 30 | T12 | Med. Bi Pin | S6667 | F30T12/SUN | Full Spectrum | 22000 | 1650 | 36" | 30 |
| 40 | T12 | Med. Bi Pin | S6409 | F40T12/BLB | Blacklight Blue | 10000 | n/a | 48" | 6 |
| 40 | T12 | Med. Bi Pin | S2926 | F40T12/BL | Blacklight | 10000 | n/a | 48" | 30 |

fluorescent lamps

Fluorescent T12 Tubes

Not Shown Actual Size

F34T12/SS

(Previously F40T12/SS)

34 Watt 48"
Energy Savers
Medium Bi Pin Base

S6600 F34T12/Cool White/SS

S6601 F34T12/Warm White/SS

Designer Series

S6602 F34T12/D30/SS

S6603 F34T12/D35/SS

S6604 F34T12/D41/SS

Designer 800 Series

S6605 F34T12/D830/SS

S6606 F34T12/D835/SS

S6607 F34T12/D841/SS

Color Reference Guide

D30/D830 = 3000K Warm White

D35/D835 = 3500K Neutral

D41/D841 = 4100K Cool White

700 Series lamps equal: 70CRI*
Good color rendition

800 Series lamps equal: 80CRI*
Superior color rendition

(Color rendering index*)

F40T12

40 Watt 48"
Standard Wattage
Medium Bi Pin Base

S2927 F40T12/Cool White Deluxe

S6608 F40T12/Daylight Deluxe

S6609 F40T12/Natural White

S6610 F40T12/Design 50

S6668 F40T12/Full Spectrum

Designer Series

S6611 F40T12/D30

S6612 F40T12/D35

S6613 F40T12/D41

Designer 800 Series

S6614 F40T12/D830

S6615 F40T12/D835

S6616 F40T12/D841

S2928 F40T12/D865

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Mst.Ctn./ Inner Pack |
|-------|-----------|-------------|-----------------|-------------|---------------------|------------------|--------|--------|----------------------|
| 34 | T12 | Med. Bi Pin | S6600 | F34/CW/SS | CW 4200K 62CRI | 20000 | 2650 | 48" | 30 |
| 34 | T12 | Med. Bi Pin | S6601 | F34/WW/SS | WW 3000K 52 CRI | 20000 | 2750 | 48" | 30 |
| 34 | T12 | Med. Bi Pin | S6602 | F34/D30/SS | 3000K 70CRI | 20000 | 2800 | 48" | 30 |
| 34 | T12 | Med. Bi Pin | S6605 | F34/D830/SS | 3000K 80CRI | 20000 | 2900 | 48" | 30 |
| 34 | T12 | Med. Bi Pin | S6603 | F34/D35/SS | 3500K 70CRI | 20000 | 2800 | 48" | 30 |
| 34 | T12 | Med. Bi Pin | S6606 | F34/D835/SS | 3500K 80CRI | 20000 | 2900 | 48" | 30 |
| 34 | T12 | Med. Bi Pin | S6604 | F34/D41/SS | 4100K 70CRI | 20000 | 2800 | 48" | 30 |
| 34 | T12 | Med. Bi Pin | S6607 | F34/D841/SS | 4100K 80CRI | 20000 | 2900 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S2927 | F40CWVX | CW Deluxe 87CRI | 20000 | 2150 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6609 | F40N | Natural 3400K 86CRI | 20000 | 2100 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6611 | F40/D30 | 3000K 70CRI | 20000 | 3200 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6614 | F40/D830 | 3000K 80CRI | 20000 | 3300 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6612 | F40/D35 | 3500K 70CRI | 20000 | 3200 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6615 | F40/D835 | 3500K 80CRI | 20000 | 3300 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6613 | F40/D41 | 4100K 70CRI | 20000 | 3200 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6616 | F40/D841 | 4100K 80CRI | 20000 | 3300 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6610 | F40/DSGN50 | 5000K 90CRI | 20000 | 2200 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6608 | F40/DX | Day 6500K 88CRI | 20000 | 2180 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S2928 | F40/D865 | 6500K 80CRI | 20000 | 3000 | 48" | 30 |
| 40 | T12 | Med. Bi Pin | S6668 | F40/SUN | Full Spectrum | 26000 | 2100 | 48" | 30 |

Fluorescent

T12 U Bend Tubes

20,000 Hours

FB34/SS

(Previously FB40T12)

34 Watt

Energy Savers
Medium Bi Pin Base

6" Leg Spacing

S6680 FB34/Cool White
S6681 FB34/Warm White

3" Leg Spacing

S6682 FB34/Cool White
S6690 FB34/Warm White

Designer Series

6" Leg Spacing

S6683 FB34/D30/SS
S6684 FB34/D35/SS
S6685 FB34/D41/SS

Packing: 12/Master

Designer series lamps
equal: 70CRI*
Good color rendition
(Color rendering index*)



Not Shown Actual Size

FB40

40 Watt

Standard Wattage
Medium Bi Pin Base

6" Leg Spacing

S6686 FB40/Daylight Deluxe

Designer Series

S6687 FB40/D30/3000K
S6688 FB40/D35/3500K
S6689 FB40/D41/4100K

Packing: 12/Master

Color Reference Guide

D30/D830 = 3000K Warm White
D35/D835 = 3500K Neutral
D41/D841 = 4100K Cool White

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Leg Spacing | Carton |
|-------|-----------|-------------|-----------------|---------------|-----------------|------------------|----------------|----------------|-------------|--------|
| 34 | T12 | Med. Bi Pin | S6680 | FB34/CW/6/SS | Cool White | 18000 | 2600 | 22.5 | 6" | 12 |
| 34 | T12 | Med. Bi Pin | S6681 | FB34/WW/6/SS | Warm White | 18000 | 2650 | 22.5 | 6" | 12 |
| 34 | T12 | Med. Bi Pin | S6683 | FB34/D30/6/SS | 3000K 70CRI | 18000 | 2730 | 22.5 | 6" | 12 |
| 34 | T12 | Med. Bi Pin | S6684 | FB34/D35/6/SS | 3500K 70CRI | 18000 | 2730 | 22.5 | 6" | 12 |
| 34 | T12 | Med. Bi Pin | S6685 | FB34/D41/6/SS | 4100K 70CRI | 18000 | 2730 | 22.5 | 6" | 12 |
| 34 | T12 | Med. Bi Pin | S6682 | FB34/CW/3/EW | Cool White | 18000 | 2350 | 22.5 | 3" | 12 |
| 34 | T12 | Med. Bi Pin | S6690 | FB34/WW/3/EW | Warm White | 18000 | 2425 | 22.5 | 3" | 12 |
| 40 | T12 | Med. Bi Pin | S6686 | FB40/DX/6 | Daylight Deluxe | 18000 | 2300 | 22.5 | 6" | 12 |
| 40 | T12 | Med. Bi Pin | S6687 | FB40/D30/6 | 3000K 70CRI | 18000 | 3050 | 22.5 | 6" | 12 |
| 40 | T12 | Med. Bi Pin | S6688 | FB40/D35/6 | 3500K 70CRI | 18000 | 3050 | 22.5 | 6" | 12 |
| 40 | T12 | Med. Bi Pin | S6689 | FB40/D41/6 | 4100K 70CRI | 18000 | 3050 | 22.5 | 6" | 12 |

Fluorescent *Slimline* Tubes

Slimline Instant Start Lamps



Not Shown Actual Size

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|------------|-----------------|-----------|-------------|------------------|----------------|----------------|--------|
| 25 | T6 | Single Pin | S6471 | F42T6/CW | Cool White | 7500 | 1750 | 42" | 24 |
| 25 | T6 | Single Pin | S2929 | F42T6/D35 | 3500K 70CRI | 7500 | 1830 | 42" | 24 |
| 25 | T6 | Single Pin | S6470 | F42T6/WW | Warm White | 7500 | 1825 | 42" | 24 |
| 38 | T6 | Single Pin | S6475 | F64T6/CW | Cool White | 7500 | 2800 | 64" | 24 |
| 38 | T6 | Single Pin | S6473 | F64T6/WW | Warm White | 7500 | 2900 | 64" | 24 |
| 38 | T8 | Single Pin | S6478 | F72T8/CW | Cool White | 7500 | 3050 | 72" | 24 |
| 38 | T8 | Single Pin | S6477 | F72T8/WW | Warm White | 7500 | 3100 | 72" | 24 |
| 38 | T8 | Single Pin | S6476 | F72T8/D | Daylight | 7500 | 2600 | 72" | 24 |
| 38 | T8 | Single Pin | S2930 | F96T8/CW | Cool White | 7500 | 4000 | 96" | 24 |
| 38 | T8 | Single Pin | S2931 | F96T8/D | Daylight | 7500 | 3550 | 96" | 24 |
| 24 | T12 | Single Pin | S6469 | F24T12/CW | Cool White | 7500 | 1150 | 24" | 30 |
| 30 | T12 | Single Pin | S6472 | F36T12/CW | Cool White | 7500 | 1970 | 36" | 30 |
| 39 | T12 | Single Pin | S6660 | F48T12/CW | Cool White | 9000 | 2875 | 48" | 30 |
| 39 | T12 | Single Pin | S6481 | F48T12/D | Daylight | 9000 | 2450 | 48" | 30 |
| 50 | T12 | Single Pin | S6661 | F60T12/CW | Cool White | 12000 | 3700 | 60" | 30 |
| 50 | T12 | Single Pin | S6483 | F60T12/D | Daylight | 12000 | 3000 | 60" | 30 |
| 52 | T12 | Single Pin | S6662 | F64T12/CW | Cool White | 12000 | 3900 | 64" | 30 |
| 52 | T12 | Single Pin | S6485 | F64T12/D | Daylight | 12000 | 3300 | 64" | 30 |
| 55 | T12 | Single Pin | S6630 | F72T12/CW | Cool White | 12000 | 4500 | 72" | 15 |
| 55 | T12 | Single Pin | S6631 | F72T12/WW | Warm White | 12000 | 4550 | 72" | 15 |
| 55 | T12 | Single Pin | S6632 | F72T12/D | Daylight | 12000 | 3800 | 72" | 15 |
| 70 | T12 | Single Pin | S6663 | F84T12/CW | Cool White | 12000 | 5300 | 84" | 15 |

Fluorescent *Slimline* Tubes



F96T12

Full Wattage
Single Pin Base

S6650 F96T12/Daylight Deluxe

S6651 F96T12/Design 50

Designer Series

S6652 F96T12/D30

S6653 F96T12/D35

S6654 F96T12/D41

Designer 800 Series

S6655 F96T12/D830

S6656 F96T12/D835

S6657 F96T12/D841

S2932 F96T12/D865

Packing: 15/Master

Color Reference Guide
D30/D830 = 3000K Warm White
D35/D835 = 3500K Neutral
D41/D841 = 4100K Cool White

Not Shown Actual Size



F96T12/SS

Energy Savers
Single Pin Base

S6640 F96T12/Cool White/SS

S6641 F96T12/Warm White/SS

Designer Series

S6642 F96T12/D30/SS

S6643 F96T12/D35/SS

S6644 F96T12/D41/SS

Designer 800 Series

S6645 F96T12/D830/SS

S6646 F96T12/D835/SS

S6647 F96T12/D841/SS

700 Series lamps equal: 70CRI*
Good color rendition

800 Series lamps equal: 80CRI*
Superior color rendition

(Color rendering index*)

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|------------|-----------------|----------------|-----------------|------------------|----------------|----------------|--------|
| 60 | T12 | Single Pin | S6640 | F96T12/CW/SS | Cool White | 12000 | 5300 | 96" | 15 |
| 60 | T12 | Single Pin | S6641 | F96T12/WW/SS | Warm White | 12000 | 5500 | 96" | 15 |
| 60 | T12 | Single Pin | S6642 | F96T12/D30/SS | 3000K 70CRI | 12000 | 5600 | 96" | 15 |
| 60 | T12 | Single Pin | S6645 | F96T12/D830/SS | 3000K 80CRI | 12000 | 5800 | 96" | 15 |
| 60 | T12 | Single Pin | S6643 | F96T12/D35/SS | 3500K 70CRI | 12000 | 5600 | 96" | 15 |
| 60 | T12 | Single Pin | S6646 | F96T12/D835/SS | 3500K 80CRI | 12000 | 5800 | 96" | 15 |
| 60 | T12 | Single Pin | S6644 | F96T12/D41/SS | 4100K 70CRI | 12000 | 5600 | 96" | 15 |
| 60 | T12 | Single Pin | S6647 | F96T12/D841/SS | 4100K 80CRI | 12000 | 5800 | 96" | 15 |
| 75 | T12 | Single Pin | S6652 | F96T12/D30 | 3000K 70CRI | 12000 | 6420 | 96" | 15 |
| 75 | T12 | Single Pin | S6655 | F96T12/D830 | 3000K 80CRI | 12000 | 6550 | 96" | 15 |
| 75 | T12 | Single Pin | S6653 | F96T12/D35 | 3500K 70CRI | 12000 | 6420 | 96" | 15 |
| 75 | T12 | Single Pin | S6656 | F96T12/D835 | 3500K 80CRI | 12000 | 6550 | 96" | 15 |
| 75 | T12 | Single Pin | S6654 | F96T12/D41 | 4100K 70CRI | 12000 | 6420 | 96" | 15 |
| 75 | T12 | Single Pin | S6657 | F96T12/D841 | 4100K 80CRI | 12000 | 6550 | 96" | 15 |
| 75 | T12 | Single Pin | S6651 | F96T12/DSGN50 | 5000K 90CRI | 12000 | 4400 | 96" | 15 |
| 75 | T12 | Single Pin | S6650 | F96T12/DX | Daylight Deluxe | 12000 | 4310 | 96" | 15 |
| 75 | T12 | Single Pin | S2932 | F96T12/D865 | 6500K 80CRI | 12000 | 6000 | 96" | 15 |

fluorescent lamps

Fluorescent **HO T12** Tubes



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Inner Pack |
|-------|-----------|---------------|-----------------|------------------|-------------|------------------|----------------|----------------|------------|
| 25 | T12 | Recessed D.C. | S2933 | F18T12/CW/HO | Cool White | 9000 | 1100 | 18" | 30 |
| 25 | T12 | Recessed D.C. | S2934 | F18T12/DSGN50/HO | 5000K 90CRI | 9000 | 850 | 18" | 30 |
| 35 | T12 | Recessed D.C. | S6449 | F24T12/CW/HO | Cool White | 9000 | 1650 | 24" | 30 |
| 35 | T12 | Recessed D.C. | S2935 | F24T12/DSGN50/HO | 5000K 90CRI | 9000 | 1200 | 24" | 30 |
| 35 | T12 | Recessed D.C. | S6450 | F24T12/D/HO | Daylight | 9000 | 1400 | 24" | 30 |
| 42 | T12 | Recessed D.C. | S6451 | F30T12/CW/HO | Cool White | 9000 | 2250 | 30" | 30 |
| 45 | T12 | Recessed D.C. | S6452 | F36T12/CW/HO | Cool White | 9000 | 2850 | 36" | 30 |
| 45 | T12 | Recessed D.C. | S2936 | F36T12/DSGN50/HO | 5000K 90CRI | 9000 | 2100 | 36" | 30 |
| 45 | T12 | Recessed D.C. | S2937 | F36T12/D/HO | Daylight | 9000 | 2500 | 36" | 30 |
| 55 | T12 | Recessed D.C. | S6453 | F42T12/CW/HO | Cool White | 9000 | 3400 | 42" | 30 |
| 55 | T12 | Recessed D.C. | S2938 | F42T12/DSGN50/HO | 5000K 90CRI | 9000 | 2550 | 42" | 30 |
| 55 | T12 | Recessed D.C. | S6454 | F42T12/D/HO | Daylight | 9000 | 3050 | 42" | 30 |
| 60 | T12 | Recessed D.C. | S6670 | F48T12/CW/HO | Cool White | 12000 | 4050 | 48" | 30 |
| 60 | T12 | Recessed D.C. | S2939 | F48T12/DSGN50/HO | 5000K 90CRI | 12000 | 3050 | 48" | 30 |
| 60 | T12 | Recessed D.C. | S2940 | F48T12/D/HO | Daylight | 12000 | 3600 | 48" | 30 |
| 75 | T12 | Recessed D.C. | S6671 | F60T12/CW/HO | Cool White | 12000 | 5200 | 60" | 30 |
| 75 | T12 | Recessed D.C. | S2941 | F60T12/DSGN50/HO | 5000K 90CRI | 12000 | 3850 | 60" | 30 |
| 75 | T12 | Recessed D.C. | S6457 | F60T12/D/HO | Daylight | 12000 | 4600 | 60" | 30 |
| 80 | T12 | Recessed D.C. | S6672 | F64T12/CW/HO | Cool White | 12000 | 5750 | 64" | 30 |
| 80 | T12 | Recessed D.C. | S2942 | F64T12/DSGN50/HO | 5000K 90CRI | 12000 | 4200 | 64" | 30 |
| 80 | T12 | Recessed D.C. | S6458 | F64T12/D/HO | Daylight | 12000 | 4900 | 64" | 30 |

Fluorescent *HO/VHO T12* Tubes



Not Shown Actual Size

fluorescent lamps

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-----------------------------------|-----------|---------------|-----------------|-------------------|-------------|------------------|----------------|----------------|--------|
| High Output (800 MA) | | | | | | | | | |
| 85 | T12 | Recessed D.C. | S6673 | F72T12/CW/HO | Cool White | 12000 | 6250 | 72" | 15 |
| 85 | T12 | Recessed D.C. | S2943 | F72T12/DSGN50/HO | 5000K 90CRI | 12000 | 4600 | 72" | 15 |
| 85 | T12 | Recessed D.C. | S6460 | F72T12/D/HO | Daylight | 12000 | 5550 | 72" | 15 |
| 85 | T12 | Recessed D.C. | S2944 | F72T12/D35/HO | 3500K 70CRI | 12000 | 6650 | 72" | 15 |
| 100 | T12 | Recessed D.C. | S6674 | F84T12/CW/HO | Cool White | 12000 | 7550 | 84" | 15 |
| 100 | T12 | Recessed D.C. | S2945 | F84T12/DSGN50/HO | 5000K 90CRI | 12000 | 5600 | 84" | 15 |
| 100 | T12 | Recessed D.C. | S6461 | F84T12/D/HO | Daylight | 12000 | 6700 | 84" | 15 |
| 95 | T12 | Recessed D.C. | S6675 | F96T12/CW/HO/SS | Cool White | 12000 | 8000 | 96" | 15 |
| 110 | T12 | Recessed D.C. | S6676 | F96T12/CW/HO-COLD | Cool White | 12000 | 8600 | 96" | 15 |
| 110 | T12 | Recessed D.C. | S2946 | F96T12/DSGN50/HO | 5000K 90CRI | 12000 | 6450 | 96" | 15 |
| 110 | T12 | Recessed D.C. | S6462 | F96T12/D/HO-COLD | Daylight | 12000 | 7600 | 96" | 15 |
| 110 | T12 | Recessed D.C. | S2947 | F96T12/D30/HO | 3000K 70CRI | 12000 | 9050 | 96" | 15 |
| 110 | T12 | Recessed D.C. | S2948 | F96T12/D35/HO | 3500K 70CRI | 12000 | 9050 | 96" | 15 |
| 110 | T12 | Recessed D.C. | S2949 | F96T12/D41/HO | 4100K 70CRI | 12000 | 9050 | 96" | 15 |
| Very High Output (1500 MA) | | | | | | | | | |
| 115 | T12 | Recessed D.C. | S6463 | F48T12/CW/VHO | Cool White | 10000 | 6600 | 48" | 30 |
| 135 | T12 | Recessed D.C. | S6465 | F60T12/CW/VHO | Cool White | 10000 | 8700 | 60" | 30 |
| 160 | T12 | Recessed D.C. | S6466 | F72T12/CW/VHO | Cool White | 10000 | 10600 | 72" | 15 |
| 195 | T12 | Recessed D.C. | S6467 | F96T12/CW/VHO/SS | Cool White | 10000 | 13000 | 96" | 15 |
| 215 | T12 | Recessed D.C. | S6677 | F96T12/CW/VHO | Cool White | 10000 | 14000 | 96" | 15 |

Fluorescent T9 Circline Tubes



fluorescent lamps



FC6T9/6.5"
20 Watt
4 Pin Base
S6509 Cool White
S2950 Warm White

FC8T9/8"
22 Watt
4 Pin Base
S6500 Cool White
S6501 Daylight
S6502 Warm White

FC12T9/12"
32 Watt
4 Pin Base
S6503 Cool White
S6504 Daylight
S6505 Warm White

FC16T9/16"
40 Watt
4 Pin Base
S6506 Cool White
S2953 Daylight
S2954 Warm White

Packing: 12/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Diameter | Carton |
|-------|-----------|-------|-----------------|-----------|-------------|------------------|----------------|----------|--------|
| 20 | T9 | 4 Pin | S6509 | FC6T9/CW | Cool White | 8000 | 750 | 6.5" | 12 |
| 20 | T9 | 4 Pin | S2950 | FC6T9/WW | Warm White | 8000 | 800 | 6.5" | 12 |
| 22 | T9 | 4 Pin | S6500 | FC8T9/CW | Cool White | 11000 | 1050 | 8" | 12 |
| 22 | T9 | 4 Pin | S6501 | FC8T9/D | Daylight | 11000 | 900 | 8" | 12 |
| 22 | T9 | 4 Pin | S6502 | FC8T9/WW | Warm White | 11000 | 1050 | 8" | 12 |
| 32 | T9 | 4 Pin | S6503 | FC12T9/CW | Cool White | 15000 | 1925 | 12" | 12 |
| 32 | T9 | 4 Pin | S6504 | FC12T9/D | Daylight | 15000 | 1650 | 12" | 12 |
| 32 | T9 | 4 Pin | S6505 | FC12T9/WW | Warm White | 15000 | 1950 | 12" | 12 |
| 40 | T9 | 4 Pin | S6506 | FC16T9/CW | Cool White | 18000 | 2750 | 16" | 12 |
| 40 | T9 | 4 Pin | S2953 | FC16T9/D | Daylight | 18000 | 2350 | 16" | 12 |
| 40 | T9 | 4 Pin | S2954 | FC16T9/WW | Warm White | 18000 | 2800 | 16" | 12 |

Fluorescent

Circline T5 Tubes

Tri-Phosphor — Electronic Ballast

12,000 Hours



Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Color/CRI | Avg. Rated Hours | Initial Lumens | Diameter | Carton |
|-------|-----------|-------|-----------------|--------------|-------------|------------------|----------------|----------|--------|
| 22 | T5 | 2GX13 | S2955 | FPC22/830 | 3000K 82CRI | 12000 | 1800 | 9" | 12 |
| 22 | T5 | 2GX13 | S2956 | FPC22/835 | 3500K 82CRI | 12000 | 1800 | 9" | 12 |
| 22 | T5 | 2GX13 | S2957 | FPC22/841 | 4100K 82CRI | 12000 | 1800 | 9" | 12 |
| 40 | T5 | 2GX13 | S2958 | FPC40/830 | 3000K 82CRI | 12000 | 3200 | 12" | 12 |
| 40 | T5 | 2GX13 | S2959 | FPC40/835 | 3500K 82CRI | 12000 | 3200 | 12" | 12 |
| 40 | T5 | 2GX13 | S2960 | FPC40/841 | 4100K 82CRI | 12000 | 3200 | 12" | 12 |
| 55 | T5 | 2GX13 | S2961 | FPC55/830/HO | 3000K 82CRI | 12000 | 4000 | 12" | 12 |
| 55 | T5 | 2GX13 | S2962 | FPC55/835/HO | 3500K 82CRI | 12000 | 4000 | 12" | 12 |
| 55 | T5 | 2GX13 | S2963 | FPC55/841/HO | 4100K 82CRI | 12000 | 4000 | 12" | 12 |

fluorescent lamps

Shatter Proof Fluorescent Lamps



T6

Single Pin Base
S6591 F42T6/CW/TF
S6692 F64T6/CW/TF
 Packing: 24/Master



T8

Electronic
Medium Bi Pin Base
S6583 FO17/741/TF
S6584 FO25/741/TF
S6585 FO32/741/TF
 Packing: 30/Master



T8

U-Bend
Medium Bi Pin Base
S6594 FBO32/741/6/TF
 Packing: 16/Master

Satco Shatter Proof Lamps feature a special **Kenlon®** coating which effectively contains glass particles should the lamp break. These lamps are perfect in use food storage

preparation, display and sorting tables, hospitals, restaurants and recreation facilities. Special orders are available for large quantities on specific lamp types.

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|-------------|-----------------|----------------|-------------|------------------|----------------|----------------|--------|
| 25 | T6 | Single Pin | S6591 | F42T6/CW/TF | Coated | 7500 | 1750 | 42" | 24 |
| 38 | T6 | Single Pin | S6592 | F64T6/CW/TF | Coated | 7500 | 2800 | 64" | 24 |
| 17 | T8 | Med. Bi-Pin | S6583 | FO17/741/TF | Coated | 20000 | 1300 | 24" | 30 |
| 25 | T8 | Med. Bi-Pin | S6584 | FO25/741/TF | Coated | 20000 | 2025 | 36" | 30 |
| 32 | T8 | Med. Bi-Pin | S6585 | FO32/741/TF | Coated | 20000 | 2750 | 48" | 30 |
| 32 | T8 | Med. Bi-Pin | S6594 | FBO32/741/6/TF | Coated | 20000 | 2750 | 22.5" | 16 |

Shatter Proof Fluorescent Lamps



T12

U-Bend Cool White

S6593 FB34CW/6/SS/TF
Packing: 12/Master



T12 Cool White

Medium Bi-Pin Base

S6579 F20T12/CW/TF
S6580 F30T12/CW/TF
S6581 F34/CW/SS/TF
Packing: 30/Master

Single Pin Base

S6586 F48T12/CW/TF
Packing: 30/Master
S6582 F96T12/CW/SS/TF
Packing: 15/Master

Recessed Double Contact Base

S6587 F48T12/CW/HO/TF
S6595 F48T12/CW/VHO/TF
Packing: 30/Master
S6588 F96T12/CW/HO/SS/TF
S6589 F96T12/CW/HO/CT/TF
S6590 F96T12/CW/VHO/TF
Packing: 15/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|--------------|-----------------|---------------------------|-------------|------------------|----------------|----------------|--------|
| 20 | T12 | Med. Bi- Pin | S6579 | F20T12/CW/TF | Coated | 9000 | 1220 | 24" | 30 |
| 30 | T12 | Med. Bi- Pin | S6580 | F30T12/CW/TF | Coated | 18000 | 2200 | 36" | 30 |
| 34 | T12 | Med. Bi- Pin | S6581 | F34T12/CW/SS/TF | Coated | 20000 | 2650 | 48" | 30 |
| 39 | T12 | Single Pin | S6586 | F48T12/CW/TF | Coated | 9000 | 2875 | 48" | 30 |
| 60 | T12 | Single Pin | S6587 | F48T12/CW/HO/TF | Coated | 20000 | 4050 | 48" | 30 |
| 115 | T12 | Single Pin | S6595 | F48T12/CW/VHO/LT/TF | Coated | 20000 | 7400 | 48" | 30 |
| 60 | T12 | Single Pin | S6582 | F96T12/CW/SS/TF | Coated | 12000 | 5300 | 96" | 15 |
| 95 | T12 | Rec. D.C. | S6588 | F96T12/CW/HO/SS/TF | Coated | 12000 | 8000 | 96" | 15 |
| 110 | T12 | Rec. D.C. | S6589 | F96T12/CW/HO/COLD TEMP/TF | Coated | 12000 | 8600 | 96" | 15 |
| 215 | T12 | Rec. D.C. | S6590 | F96T12/CW/VHO/TF | Coated | 10000 | 14000 | 96" | 15 |
| 34 | T12 | Med. Bi- Pin | S6593 | FB34/CW/6/SS/TF | Coated | 18000 | 2600 | 22.5" | 12 |

fluorescent lamps

Compact Fluorescent

Twin Tubes **SATCO**[®]

Not Shown Actual Size

10,000 Hours



CFS5

5 Watt
G23 Base

S6300 CFS5W/827
S6301 CFS5W/841

Packing:
50/Master,
Individually Boxed



CFS7

7 Watt
G23 Base

S6302 CFS7W/827
S6303 CFS7W/835
S6304 CFS7W/841
S6305 CFS7W/850

Packing:
50/Master,
Individually Boxed



CFS9

9 Watt
G23 Base

S6306 CFS9W/827
S6307 CFS9W/835
S6308 CFS9W/841
S6309 CFS9W/850

Packing:
50/Master,
Individually Boxed



CFS13

13 Watt
GX23 Base

S6310 CFS13W/827
S6380 CFS13W/830
S6311 CFS13W/835
S6312 CFS13W/841
S6313 CFS13W/850

Packing:
50/Master,
Individually Boxed

SATCO COMPACT FLUORESCENT LAMPS QUALITY • VALUE • PERFORMANCE

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Pack. Type | Mst.Ctn./Inner Pack |
|-------|-----------|------|-----------------|------------|-------------|------------------|--------|--------|------------|---------------------|
| 5 | T4 | G23 | S6300 | CFS5W/827 | 2700K 82CRI | 10000 | 230 | 4.2" | Box | 50/5 |
| 5 | T4 | G23 | S6301 | CFS5W/841 | 4100K 82CRI | 10000 | 230 | 4.2" | Box | 50/5 |
| 7 | T4 | G23 | S6302 | CFS7W/827 | 2700K 82CRI | 10000 | 400 | 5.3" | Box | 50/5 |
| 7 | T4 | G23 | S6303 | CFS7W/835 | 3500K 82CRI | 10000 | 400 | 5.3" | Box | 50/5 |
| 7 | T4 | G23 | S6304 | CFS7W/841 | 4100K 82CRI | 10000 | 400 | 5.3" | Box | 50/5 |
| 7 | T4 | G23 | S6305 | CFS7W/850 | 5000K 82CRI | 10000 | 400 | 5.3" | Box | 50/5 |
| 9 | T4 | G23 | S6306 | CFS9W/827 | 2700K 82CRI | 10000 | 580 | 6.5" | Box | 50/5 |
| 9 | T4 | G23 | S6307 | CFS9W/835 | 3500K 82CRI | 10000 | 580 | 6.5" | Box | 50/5 |
| 9 | T4 | G23 | S6308 | CFS9W/841 | 4100K 82CRI | 10000 | 580 | 6.5" | Box | 50/5 |
| 9 | T4 | G23 | S6309 | CFS9W/850 | 5000K 82CRI | 10000 | 580 | 6.5" | Box | 50/5 |
| 13 | T4 | GX23 | S6310 | CFS13W/827 | 2700K 82CRI | 10000 | 800 | 7.1" | Box | 50/5 |
| 13 | T4 | GX23 | S6380 | CFS13W/830 | 3000K 82CRI | 10000 | 800 | 7.1" | Box | 50/5 |
| 13 | T4 | GX23 | S6311 | CFS13W/835 | 3500K 82CRI | 10000 | 800 | 7.1" | Box | 50/5 |
| 13 | T4 | GX23 | S6312 | CFS13W/841 | 4100K 82CRI | 10000 | 800 | 7.1" | Box | 50/5 |
| 13 | T4 | GX23 | S6313 | CFS13W/850 | 5000K 82CRI | 10000 | 800 | 7.1" | Box | 50/5 |

fluorescent lamps



Compact Fluorescent

10000 Hours

Two Pin Quad Tubes

Not Shown
Actual Size



CFD26

26 Watt
G24d-3 2 Pin Base
S6325 CFD26W/827
S6326 CFD26W/830
S6327 CFD26W/835
S6328 CFD26W/841

Packing:
50/Master,
Individually Boxed



CFD18

18 Watt
G24d-2 2 Pin Base
S6321 CFD18W/827
S6322 CFD18W/830
S6323 CFD18W/835
S6324 CFD18W/841

Packing:
50/Master,
Individually Boxed



CFD13

13 Watt
GX23-2 2 Pin Base
S6317 CFD13W/827
S6318 CFD13W/830
S6319 CFD13W/835
S6320 CFD13W/841

Packing:
50/Master,
Individually Boxed



CFD9

9 Watt
G23-2 2 Pin Base
S6314 CFD9W/827
S6315 CFD9W/830
S6316 CFD9W/835

Packing:
50/Master,
Individually Boxed

fluorescent lamps

SATCO COMPACT FLUORESCENT LAMPS QUALITY • VALUE • PERFORMANCE

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Mst.Ctn./ Inner Pack |
|-------|-----------|--------|-----------------|------------|-------------|------------------|----------------|----------------|----------------------|
| 9 | T4 | G23-2 | S6314 | CFD9W/827 | 2700K 82CRI | 10000 | 525 | 4.3" | 50/5 |
| 9 | T4 | G23-2 | S6315 | CFD9W/830 | 3000K 82CRI | 10000 | 525 | 4.3" | 50/5 |
| 9 | T4 | G23-2 | S6316 | CFD9W/835 | 3500K 82CRI | 10000 | 525 | 4.3" | 50/5 |
| 13 | T4 | GX23-2 | S6317 | CFD13W/827 | 2700K 82CRI | 10000 | 780 | 4.6" | 50/5 |
| 13 | T4 | GX23-2 | S6318 | CFD13W/830 | 3000K 82CRI | 10000 | 780 | 4.6" | 50/5 |
| 13 | T4 | GX23-2 | S6319 | CFD13W/835 | 3500K 82CRI | 10000 | 780 | 4.6" | 50/5 |
| 13 | T4 | GX23-2 | S6320 | CFD13W/841 | 4100K 82CRI | 10000 | 780 | 4.6" | 50/5 |
| 18 | T4 | G24D-2 | S6321 | CFD18W/827 | 2700K 82CRI | 10000 | 1250 | 6.0" | 50/5 |
| 18 | T4 | G24D-2 | S6322 | CFD18W/830 | 3000K 82CRI | 10000 | 1250 | 6.0" | 50/5 |
| 18 | T4 | G24D-2 | S6323 | CFD18W/835 | 3500K 82CRI | 10000 | 1250 | 6.0" | 50/5 |
| 18 | T4 | G24D-2 | S6324 | CFD18W/841 | 4100K 82CRI | 10000 | 1250 | 6.0" | 50/5 |
| 26 | T4 | G24D-3 | S6325 | CFD26W/827 | 2700K 82CRI | 10000 | 1825 | 6.8" | 50/5 |
| 26 | T4 | G24D-3 | S6326 | CFD26W/830 | 3000K 82CRI | 10000 | 1825 | 6.8" | 50/5 |
| 26 | T4 | G24D-3 | S6327 | CFD26W/835 | 3500K 82CRI | 10000 | 1825 | 6.8" | 50/5 |
| 26 | T4 | G24D-3 | S6328 | CFD26W/841 | 4100K 82CRI | 10000 | 1825 | 6.8" | 50/5 |

Compact Fluorescent *Four Pin* Electronic



Not Shown Actual Size



CFD13W/4P

13 Watt
G24q-1 4 Pin Base

- S6329** CFD13W/4P/827
- S6330** CFD13W/4P/830
- S6331** CFD13W/4P/835
- S6332** CFD13W/4P/841

Packing:
50/Master,
Individually Boxed



CFD18W/4P

18 Watt
G24q-2 4 Pin Base

- S6333** CFD18W/4P/827
- S6334** CFD18W/4P/830
- S6335** CFD18W/4P/835
- S6336** CFD18W/4P/841

Packing:
50/Master,
Individually Boxed



CFD26W/4P

26 Watt
G24q-3 4 Pin Base

- S6337** CFD26W/4P/827
- S6338** CFD26W/4P/830
- S6339** CFD26W/4P/835
- S6340** CFD26W/4P/841

Packing:
50/Master,
Individually Boxed

SATCO COMPACT FLUORESCENT LAMPS QUALITY • VALUE • PERFORMANCE

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Mst. Ctn./ Inner Pack. |
|-------|-----------|--------|-----------------|---------------|-------------|------------------|----------------|----------------|------------------------|
| 13 | T4 | G24q-1 | S6329 | CFD13W/4P/827 | 2700K 82CRI | 12000 | 900 | 5.2" | 50/5 |
| 13 | T4 | G24q-1 | S6330 | CFD13W/4P/830 | 3000K 82CRI | 12000 | 900 | 5.2" | 50/5 |
| 13 | T4 | G24q-1 | S6331 | CFD13W/4P/835 | 3500K 82CRI | 12000 | 900 | 5.2" | 50/5 |
| 13 | T4 | G24q-1 | S6332 | CFD13W/4P/841 | 4100K 82CRI | 12000 | 900 | 5.2" | 50/5 |
| 18 | T4 | G24q-2 | S6333 | CFD18W/4P/827 | 2700K 82CRI | 12000 | 1250 | 5.8" | 50/5 |
| 18 | T4 | G24q-2 | S6334 | CFD18W/4P/830 | 3000K 82CRI | 12000 | 1250 | 5.8" | 50/5 |
| 18 | T4 | G24q-2 | S6335 | CFD18W/4P/835 | 3500K 82CRI | 12000 | 1250 | 5.8" | 50/5 |
| 18 | T4 | G24q-2 | S6336 | CFD18W/4P/841 | 4100K 82CRI | 12000 | 1250 | 5.8" | 50/5 |
| 26 | T4 | G24q-3 | S6337 | CFD26W/4P/827 | 2700K 82CRI | 12000 | 1825 | 6.5" | 50/5 |
| 26 | T4 | G24q-3 | S6338 | CFD26W/4P/830 | 3000K 82CRI | 12000 | 1825 | 6.5" | 50/5 |
| 26 | T4 | G24q-3 | S6339 | CFD26W/4P/835 | 3500K 82CRI | 12000 | 1825 | 6.5" | 50/5 |
| 26 | T4 | G24q-3 | S6340 | CFD26W/4P/841 | 4100K 82CRI | 12000 | 1825 | 6.5" | 50/5 |

fluorescent lamps



Compact Fluorescent Four Pin Electronic Triple Tube



CFT13W/4P

13 Watt
GX24q-1 4 Pin Base
S6496 CFT13W/4P/830
S6497 CFT13W/4P/835
S6498 CFT13W/4P/841

CFT18W/4P

18 Watt
GX24q-2 4 Pin Base
S6342 CFT18W/4P/830
S6343 CFT18W/4P/835
S6344 CFT18W/4P/841

CFT26W/4P

26 Watt
GX24q-3 4 Pin Base
S6346 CFT26W/4P/830
S6347 CFT26W/4P/835
S6348 CFT26W/4P/841

CFT32W/4P

32 Watt
GX24q-3 4 Pin Base
S6350 CFT32W/4P/830
S6351 CFT32W/4P/835
S6352 CFT32W/4P/841

CFT42W/4P

42 Watt
GX24q-4 4 Pin Base
S6354 CFT42W/4P/830
S6355 CFT42W/4P/835
S6356 CFT42W/4P/841

Not Shown
Actual Size

Packing:
50/Master,
Individually Boxed

SATCO COMPACT FLUORESCENT LAMPS
QUALITY • VALUE • PERFORMANCE

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|---------|-----------------|---------------|-------------|------------------|--------|--------|------------|----------------------|
| 13 | T4 | GX24Q-1 | S6496 | CFT13W/4P/830 | 3000K 82CRI | 12000 | 900 | 4.2" | Box | 50/5 |
| 13 | T4 | GX24Q-1 | S6497 | CFT13W/4P/835 | 3500K 82CRI | 12000 | 900 | 4.2" | Box | 50/5 |
| 13 | T4 | GX24Q-1 | S6498 | CFT13W/4P/841 | 4100K 82CRI | 12000 | 900 | 4.2" | Box | 50/5 |
| 18 | T4 | GX24q-2 | S6342 | CFT18W/4P/830 | 3000K 82CRI | 12000 | 1200 | 4.4" | Box | 50/5 |
| 18 | T4 | GX24q-2 | S6343 | CFT18W/4P/835 | 3500K 82CRI | 12000 | 1200 | 4.4" | Box | 50/5 |
| 18 | T4 | GX24q-2 | S6344 | CFT18W/4P/841 | 4100K 82CRI | 12000 | 1200 | 4.4" | Box | 50/5 |
| 26 | T4 | GX24q-3 | S6346 | CFT26W/4P/830 | 3000K 82CRI | 12000 | 1800 | 5.0" | Box | 50/5 |
| 26 | T4 | GX24q-3 | S6347 | CFT26W/4P/835 | 3500K 82CRI | 12000 | 1800 | 5.0" | Box | 50/5 |
| 26 | T4 | GX24q-3 | S6348 | CFT26W/4P/841 | 4100K 82CRI | 12000 | 1800 | 5.0" | Box | 50/5 |
| 32 | T4 | GX24q-3 | S6350 | CFT32W/4P/830 | 3000K 82CRI | 12000 | 2400 | 5.6" | Box | 50/5 |
| 32 | T4 | GX24q-3 | S6351 | CFT32W/4P/835 | 3500K 82CRI | 12000 | 2400 | 5.6" | Box | 50/5 |
| 32 | T4 | GX24q-3 | S6352 | CFT32W/4P/841 | 4100K 82CRI | 12000 | 2400 | 5.6" | Box | 50/5 |
| 42 | T4 | GX24q-4 | S6354 | CFT42W/4P/830 | 3000K 82CRI | 12000 | 3200 | 6.5" | Box | 50/5 |
| 42 | T4 | GX24q-4 | S6355 | CFT42W/4P/835 | 3500K 82CRI | 12000 | 3200 | 6.5" | Box | 50/5 |
| 42 | T4 | GX24q-4 | S6356 | CFT42W/4P/841 | 4100K 82CRI | 12000 | 3200 | 6.5" | Box | 50/5 |

fluorescent lamps

Compact Fluorescent *Twin* Tubes

Not Shown Actual Size

10,000 Hours



CF5DS

**5 Watt
G23 Base**

S6700 CF5DS/827
S6701 CF5DS/841

Packing:
50/Master,
Individually Boxed



CF7DS

**7 Watt
G23 Base**

S6702 CF7DS/827
S6703 CF7DS/835
S6704 CF7DS/841
S6705 CF7DS/850

Packing:
50/Master,
Individually Boxed



CF9DS

**9 Watt
G23 Base**

S6706 CF9DS/827
S6707 CF9DS/835
S6708 CF9DS/841
S6709 CF9DS/850

Packing:
50/Master,
Individually Boxed



CF13DS

**13 Watt
GX23 Base**

S6710 CF13DS/827
S6780 CF13DS/830
S6711 CF13DS/835
S6712 CF13DS/841
S6713 CF13DS/850

Packing:
50/Master,
Individually Boxed

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|------|-----------------|------------|-------------|------------------|--------|--------|------------|-----------------------|
| 5 | T4 | G23 | S6700 | CF5DS/827 | 2700K 82CRI | 10000 | 230 | 4.2" | Box | 50 |
| 5 | T4 | G23 | S6701 | CF5DS/841 | 4100K 82CRI | 10000 | 230 | 4.2" | Box | 50 |
| 7 | T4 | G23 | S6702 | CF7DS/827 | 2700K 82CRI | 10000 | 400 | 5.3" | Box | 50 |
| 7 | T4 | G23 | S6703 | CF7DS/835 | 3500K 82CRI | 10000 | 400 | 5.3" | Box | 50 |
| 7 | T4 | G23 | S6704 | CF7DS/841 | 4100K 82CRI | 10000 | 400 | 5.3" | Box | 50 |
| 7 | T4 | G23 | S6705 | CF7DS/850 | 5000K 82CRI | 10000 | 400 | 5.3" | Box | 50 |
| 9 | T4 | G23 | S6706 | CF9DS/827 | 2700K 82CRI | 10000 | 580 | 6.5" | Box | 50 |
| 9 | T4 | G23 | S6707 | CF9DS/835 | 3500K 82CRI | 10000 | 580 | 6.5" | Box | 50 |
| 9 | T4 | G23 | S6708 | CF9DS/841 | 4100K 82CRI | 10000 | 580 | 6.5" | Box | 50 |
| 9 | T4 | G23 | S6709 | CF9DS/850 | 5000K 82CRI | 10000 | 580 | 6.5" | Box | 50 |
| 13 | T4 | GX23 | S6710 | CF13DS/827 | 2700K 82CRI | 10000 | 800 | 7.1" | Box | 50 |
| 13 | T4 | GX23 | S6780 | CF13DS/830 | 3000K 82CRI | 10000 | 800 | 7.1" | Box | 50 |
| 13 | T4 | GX23 | S6711 | CF13DS/835 | 3500K 82CRI | 10000 | 800 | 7.1" | Box | 50 |
| 13 | T4 | GX23 | S6712 | CF13DS/841 | 4100K 82CRI | 10000 | 800 | 7.1" | Box | 50 |
| 13 | T4 | GX23 | S6713 | CF13DS/850 | 5000K 82CRI | 10000 | 800 | 7.1" | Box | 50 |

Compact Fluorescent *Four Pin* Tubes

10,000 Hours

Not Shown Actual Size



CF13DS/E

13 Watt

2G7 4 Pin Base

S6417 CF13DS/E/827

S6418 CF13DS/E/830

S6419 CF13DS/E/841

Packing:

50/Master,

Individually Boxed



CF9DS/E

9 Watt

2G7 4 Pin Base

S6415 CF9DS/E/827

S6416 CF9DS/E/841

Packing:

50/Master,

Individually Boxed



CF7DS/E

7 Watt

2G7 4 Pin Base

S6413 CF7DS/E/827

S6414 CF7DS/E/841

Packing:

50/Master,

Individually Boxed



CF5DS/E

5 Watt

2G7 4 Pin Base

S6411 CF5DS/E/827

S6412 CF5DS/E/841

Packing:

50/Master,

Individually Boxed

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Pack. Type | Mst.Ctn./ Inner Pack |
|-------|-----------|------|-----------------|--------------|-------------|------------------|--------|--------|------------|----------------------|
| 5 | T4 | 2G7 | S6411 | CF5DS/E/827 | 2700K 82CRI | 10000 | 230 | 3.4" | Box | 50 |
| 5 | T4 | 2G7 | S6412 | CF5DS/E/841 | 4100K 82CRI | 10000 | 230 | 3.4" | Box | 50 |
| 7 | T4 | 2G7 | S6413 | CF7DS/E/827 | 2700K 82CRI | 10000 | 400 | 4.5" | Box | 50 |
| 7 | T4 | 2G7 | S6414 | CF7DS/E/841 | 4100K 82CRI | 10000 | 400 | 4.5" | Box | 50 |
| 9 | T4 | 2G7 | S6415 | CF9DS/E/827 | 2700K 82CRI | 10000 | 580 | 5.7" | Box | 50 |
| 9 | T4 | 2G7 | S6416 | CF9DS/E/841 | 4100K 82CRI | 10000 | 580 | 5.7" | Box | 50 |
| 13 | T4 | 2GX7 | S6417 | CF13DS/E/827 | 2700K 82CRI | 10000 | 800 | 6.2" | Box | 50 |
| 13 | T4 | 2GX7 | S6418 | CF13DS/E/830 | 3000K 82CRI | 10000 | 800 | 6.2" | Box | 50 |
| 13 | T4 | 2GX7 | S6419 | CF13DS/E/841 | 4100K 82CRI | 10000 | 800 | 6.2" | Box | 50 |

fluorescent lamps

Compact Fluorescent

Two Pin *10,000 Hours* Quad Tubes

Not Shown
Actual Size



CF9DD

9 Watt

G23-2 2 Pin Base

S6714 CF9DD/827

S6715 CF9DD/830

S6716 CF9DD/835

Packing:
50/Master,
Individually Boxed



CF13DD

13 Watt

GX23-2 2 Pin Base

S6717 CF13DD/827

S6718 CF13DD/830

S6719 CF13DD/835

S6720 CF13DD/841

Packing:
50/Master,
Individually Boxed



CF18DD

18 Watt

G24d-2 2 Pin Base

S6721 CF18DD/827

S6722 CF18DD/830

S6723 CF18DD/835

S6724 CF18DD/841

Packing:
50/Master,
Individually Boxed



CF26DD

26 Watt

G24d-3 2 Pin Base

S6725 CF26DD/827

S6726 CF26DD/830

S6727 CF26DD/835

S6728 CF26DD/841

Packing:
50/Master,
Individually Boxed

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|--------|-----------------|------------|-------------|------------------|----------------|----------------|--------|
| 9 | T4 | G23-2 | S6714 | CF9DD/827 | 2700K 82CRI | 10000 | 525 | 4.3" | 50 |
| 9 | T4 | G23-2 | S6715 | CF9DD/830 | 3000K 82CRI | 10000 | 525 | 4.3" | 50 |
| 9 | T4 | G23-2 | S6716 | CF9DD/835 | 3500K 82CRI | 10000 | 525 | 4.3" | 50 |
| 13 | T4 | GX23-2 | S6717 | CF13DD/827 | 2700K 82CRI | 10000 | 780 | 4.6" | 50 |
| 13 | T4 | GX23-2 | S6718 | CF13DD/830 | 3000K 82CRI | 10000 | 780 | 4.6" | 50 |
| 13 | T4 | GX23-2 | S6719 | CF13DD/835 | 3500K 82CRI | 10000 | 780 | 4.6" | 50 |
| 13 | T4 | GX23-2 | S6720 | CF13DD/841 | 4100K 82CRI | 10000 | 780 | 4.6" | 50 |
| 18 | T4 | G24D-2 | S6721 | CF18DD/827 | 2700K 82CRI | 10000 | 1250 | 6.0" | 50 |
| 18 | T4 | G24D-2 | S6722 | CF18DD/830 | 3000K 82CRI | 10000 | 1250 | 6.0" | 50 |
| 18 | T4 | G24D-2 | S6723 | CF18DD/835 | 3500K 82CRI | 10000 | 1250 | 6.0" | 50 |
| 18 | T4 | G24D-2 | S6724 | CF18DD/841 | 4100K 82CRI | 10000 | 1250 | 6.0" | 50 |
| 26 | T4 | G24D-3 | S6725 | CF26DD/827 | 2700K 82CRI | 10000 | 1825 | 6.8" | 50 |
| 26 | T4 | G24D-3 | S6726 | CF26DD/830 | 3000K 82CRI | 10000 | 1825 | 6.8" | 50 |
| 26 | T4 | G24D-3 | S6727 | CF26DD/835 | 3500K 82CRI | 10000 | 1825 | 6.8" | 50 |
| 26 | T4 | G24D-3 | S6728 | CF26DD/841 | 4100K 82CRI | 10000 | 1825 | 6.8" | 50 |

Compact Fluorescent *Four Pin* Electronic

Not Shown Actual Size



CF26DD/E

26 Watt

G24q-3 4 Pin Base

- S6737** CF26DD/E/827
- S6738** CF26DD/E/830
- S6739** CF26DD/E/835
- S6740** CF26DD/E/841

Packing:
50/Master,
Individually Boxed



CF18DD/E

18 Watt

G24q-2 4 Pin Base

- S6733** CF18DD/E/827
- S6734** CF18DD/E/830
- S6735** CF18DD/E/835
- S6736** CF18DD/E/841

Packing:
50/Master,
Individually Boxed



CF13DD/E

13 Watt

G24q-1 4 Pin Base

- S6729** CF13DD/E/827
- S6730** CF13DD/E/830
- S6731** CF13DD/E/835
- S6732** CF13DD/E/841

Packing:
50/Master,
Individually Boxed

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|--------|-----------------|--------------|-------------|------------------|----------------|----------------|--------|
| 13 | T4 | G24q-1 | S6729 | CF13DD/E/827 | 2700K 82CRI | 12000 | 900 | 5.2" | 50 |
| 13 | T4 | G24q-1 | S6730 | CF13DD/E/830 | 3000K 82CRI | 12000 | 900 | 5.2" | 50 |
| 13 | T4 | G24q-1 | S6731 | CF13DD/E/835 | 3500K 82CRI | 12000 | 900 | 5.2" | 50 |
| 13 | T4 | G24q-1 | S6732 | CF13DD/E/841 | 4100K 82CRI | 12000 | 900 | 5.2" | 50 |
| 18 | T4 | G24q-2 | S6733 | CF18DD/E/827 | 2700K 82CRI | 12000 | 1250 | 5.8" | 50 |
| 18 | T4 | G24q-2 | S6734 | CF18DD/E/830 | 3000K 82CRI | 12000 | 1250 | 5.8" | 50 |
| 18 | T4 | G24q-2 | S6735 | CF18DD/E/835 | 3500K 82CRI | 12000 | 1250 | 5.8" | 50 |
| 18 | T4 | G24q-2 | S6736 | CF18DD/E/841 | 4100K 82CRI | 12000 | 1250 | 5.8" | 50 |
| 26 | T4 | G24q-3 | S6737 | CF26DD/E/827 | 2700K 82CRI | 12000 | 1825 | 6.5" | 50 |
| 26 | T4 | G24q-3 | S6738 | CF26DD/E/830 | 3000K 82CRI | 12000 | 1825 | 6.5" | 50 |
| 26 | T4 | G24q-3 | S6739 | CF26DD/E/835 | 3500K 82CRI | 12000 | 1825 | 6.5" | 50 |
| 26 | T4 | G24q-3 | S6740 | CF26DD/E/841 | 4100K 82CRI | 12000 | 1825 | 6.5" | 50 |

fluorescent lamps

Compact Fluorescent

Four Pin Electronic

Triple Tube

Color Reference Guide

827 = 2700K Warm White
 830 = 3000K Soft White
 835 = 3500K Neutral
 841 = 4100K Cool White



CF13DT/E

13 Watt

G24q-1 4 Pin Base

S4369 CF13DT/E/827
S4370 CF13DT/E/830
S4371 CF13DT/E/835
S4372 CF13DT/E/841

Packing:50/Master,
 Individually Boxed



CF18DT/E

18 Watt

GX24q-2 4 Pin Base

S6741 CF18DT/E/IN/827
S6742 CF18DT/E/IN/830
S6743 CF18DT/E/IN/835
S6744 CF18DT/E/IN/841

Packing:50/Master,
 Individually Boxed



CF26DT/E

26 Watt

GX24q-3 4 Pin Base

S6745 CF26DT/E/IN/827
S6746 CF26DT/E/IN/830
S6747 CF26DT/E/IN/835
S6748 CF26DT/E/IN/841

Packing:50/Master,
 Individually Boxed

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|---------|-----------------|-----------------|-------------|------------------|----------------|----------------|--------|
| 13 | T4 | GX24Q-1 | S4369 | CF13DT/E/827 | 2700K 82CRI | 12000 | 900 | 4.2" | 50 |
| 13 | T4 | GX24Q-1 | S4370 | CF13DT/E/830 | 3000K 82CRI | 12000 | 900 | 4.2" | 50 |
| 13 | T4 | GX24Q-1 | S4371 | CF13DT/E/835 | 3500K 82CRI | 12000 | 900 | 4.2" | 50 |
| 13 | T4 | GX24Q-1 | S4372 | CF13DT/E/841 | 4100K 82CRI | 12000 | 900 | 4.2" | 50 |
| 18 | T4 | GX24q-2 | S6741 | CF18DT/E/IN/827 | 2700K 82CRI | 12000 | 1200 | 4.4" | 50 |
| 18 | T4 | GX24q-2 | S6742 | CF18DT/E/IN/830 | 3000K 82CRI | 12000 | 1200 | 4.4" | 50 |
| 18 | T4 | GX24q-2 | S6743 | CF18DT/E/IN/835 | 3500K 82CRI | 12000 | 1200 | 4.4" | 50 |
| 18 | T4 | GX24q-2 | S6744 | CF18DT/E/IN/841 | 4100K 82CRI | 12000 | 1200 | 4.4" | 50 |
| 26 | T4 | GX24q-3 | S6745 | CF26DT/E/IN/827 | 2700K 82CRI | 12000 | 1800 | 5.0" | 50 |
| 26 | T4 | GX24q-3 | S6746 | CF26DT/E/IN/830 | 3000K 82CRI | 12000 | 1800 | 5.0" | 50 |
| 26 | T4 | GX24q-3 | S6747 | CF26DT/E/IN/835 | 3500K 82CRI | 12000 | 1800 | 5.0" | 50 |
| 26 | T4 | GX24q-3 | S6748 | CF26DT/E/IN/841 | 4100K 82CRI | 12000 | 1800 | 5.0" | 50 |

Compact Fluorescent

Four Pin Electronic

Triple Tube

Not Shown Actual Size



CF57DT/E

57 Watt

GX24q-5 4 Pin Base

- S6421** CF57DT/E/IN/827
- S6422** CF57DT/E/IN/830
- S6423** CF57DT/E/IN/835
- S6424** CF57DT/E/IN/841

Packing:
50/Master,
Individually Boxed



CF42DT/E

42 Watt

GX24q-4 4 Pin Base

- S6753** CF42DT/E/IN/827
- S6754** CF42DT/E/IN/830
- S6755** CF42DT/E/IN/835
- S6756** CF42DT/E/IN/841

Packing:
50/Master,
Individually Boxed



CF32DT/E

32 Watt

GX24q-3 4 Pin Base

- S6749** CF32DT/E/IN/827
- S6750** CF32DT/E/IN/830
- S6751** CF32DT/E/IN/835
- S6752** CF32DT/E/IN/841

Packing:
50/Master,
Individually Boxed

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|---------|-----------------|-----------------|-------------|------------------|--------|--------|------------|-----------------------|
| 32 | T4 | GX24q-3 | S6749 | CF32DT/E/IN/827 | 2700K 82CRI | 12000 | 2400 | 5.6" | Box | 50 |
| 32 | T4 | GX24q-3 | S6750 | CF32DT/E/IN/830 | 3000K 82CRI | 12000 | 2400 | 5.6" | Box | 50 |
| 32 | T4 | GX24q-3 | S6751 | CF32DT/E/IN/835 | 3500K 82CRI | 12000 | 2400 | 5.6" | Box | 50 |
| 32 | T4 | GX24q-3 | S6752 | CF32DT/E/IN/841 | 4100K 82CRI | 12000 | 2400 | 5.6" | Box | 50 |
| 42 | T4 | GX24q-4 | S6753 | CF42DT/E/IN/827 | 2700K 82CRI | 12000 | 3200 | 6.5" | Box | 50 |
| 42 | T4 | GX24q-4 | S6754 | CF42DT/E/IN/830 | 3000K 82CRI | 12000 | 3200 | 6.5" | Box | 50 |
| 42 | T4 | GX24q-4 | S6755 | CF42DT/E/IN/835 | 3500K 82CRI | 12000 | 3200 | 6.5" | Box | 50 |
| 42 | T4 | GX24q-4 | S6756 | CF42DT/E/IN/841 | 4100K 82CRI | 12000 | 3200 | 6.5" | Box | 50 |
| 57 | T4 | GX24q-5 | S6421 | CF57DT/E/IN/827 | 2700K 82CRI | 12000 | 4300 | 7.76" | Box | 50 |
| 57 | T4 | GX24q-5 | S6422 | CF57DT/E/IN/830 | 3000K 82CRI | 12000 | 4300 | 7.76" | Box | 50 |
| 57 | T4 | GX24q-5 | S6423 | CF57DT/E/IN/835 | 3500K 82CRI | 12000 | 4300 | 7.76" | Box | 50 |
| 57 | T4 | GX24q-5 | S6424 | CF57DT/E/IN/841 | 4100K 82CRI | 12000 | 4300 | 7.76" | Box | 50 |

fluorescent lamps

Compact Fluorescent

Long Twin Tube

2G11 Base

fluorescent lamps



18 Watt

S6757 FT18DL/830
S2964 FT18DL/830/RS
S6758 FT18DL/835
S2965 FT18DL/835/RS
S6759 FT18DL/841
S2966 FT18DL/841/RS

40 Watt

S6766 FT40DL/830/RS
S6767 FT40DL/835/RS
S6768 FT40DL/841/RS

24 Watt

S6760 FT24DL/830
S6761 FT24DL/835
S6762 FT24DL/841

50 Watt

S2967 PLL50W/830/RS
S2968 PLL50W/835/RS
S2969 PLL50W/841/RS

36 Watt

S6763 FT36DL/830
S6764 FT36DL/835
S6765 FT36DL/841

55 Watt

S6769 FT55DL/830
S6770 FT55DL/835
S6771 FT55DL/841

Color Reference Guide

830 = 3000K Soft White
 835 = 3500K Neutral
 841 = 4100K Cool White

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Description | Avg. Rated Hours | Initial Lumens | Nominal Length | Carton |
|-------|-----------|------|-----------------|----------------|-------------|------------------|----------------|----------------|--------|
| 18 | T5 | 2G11 | S6757 | FT18DL/830 | 3000K 82CRI | 12000 | 1250 | 9.0" | 10 |
| 18 | T5 | 2G11 | S2964 | FT18DL/830/RS | 3000K 82CRI | 20000 | 1250 | 10.5" | 10 |
| 18 | T5 | 2G11 | S6758 | FT18DL/835 | 3500K 82CRI | 12000 | 1250 | 9.0" | 10 |
| 18 | T5 | 2G11 | S2965 | FT18DL/835/RS | 3500K 82CRI | 20000 | 1250 | 10.5" | 10 |
| 18 | T5 | 2G11 | S6759 | FT18DL/841 | 4100K 82CRI | 12000 | 1250 | 9.0" | 10 |
| 18 | T5 | 2G11 | S2966 | FT18DL/841/RS | 4100K 82CRI | 20000 | 1250 | 10.5" | 10 |
| 24 | T5 | 2G11 | S6760 | FT24DL/830 | 3000K 82CRI | 12000 | 1800 | 12.9" | 10 |
| 24 | T5 | 2G11 | S6761 | FT24DL/835 | 3500K 82CRI | 12000 | 1800 | 12.9" | 10 |
| 24 | T5 | 2G11 | S6762 | FT24DL/841 | 4100K 82CRI | 12000 | 1800 | 12.9" | 10 |
| 36 | T5 | 2G11 | S6763 | FT36DL/830 | 3000K 82CRI | 12000 | 2900 | 16.6" | 10 |
| 36 | T5 | 2G11 | S6764 | FT36DL/835 | 3500K 82CRI | 12000 | 2900 | 16.6" | 10 |
| 36 | T5 | 2G11 | S6765 | FT36DL/841 | 4100K 82CRI | 12000 | 2900 | 16.6" | 10 |
| 40 | T5 | 2G11 | S6766 | FT40DL/830/RS | 3000K 82CRI | 20000 | 3150 | 22.6" | 10 |
| 40 | T5 | 2G11 | S6767 | FT40DL/835/RS | 3500K 82CRI | 20000 | 3150 | 22.6" | 10 |
| 40 | T5 | 2G11 | S6768 | FT40DL/841/RS | 4100K 82CRI | 20000 | 3150 | 22.6" | 10 |
| 50 | T5 | 2G11 | S2967 | PLL 50W/830/RS | 3000K 82CRI | 14000 | 4300 | 22.5" | 25 |
| 50 | T5 | 2G11 | S2968 | PLL 50W/835/RS | 3500K 82CRI | 14000 | 4300 | 22.5" | 25 |
| 50 | T5 | 2G11 | S2969 | PLL50W/841/RS | 4100K 82CRI | 14000 | 4300 | 22.5" | 25 |
| 55 | T5 | 2G11 | S6769 | FT55DL/830 | 3000K 82CRI | 12000 | 4800 | 21.1" | 10 |
| 55 | T5 | 2G11 | S6770 | FT55DL/835 | 3500K 82CRI | 12000 | 4800 | 21.1" | 10 |
| 55 | T5 | 2G11 | S6771 | FT55DL/841 | 4100K 82CRI | 12000 | 4800 | 21.1" | 10 |

Compact Fluorescent *Specialty* Tubes



Dulux-T

18 Watt

S4367 CF18DT/827

26 Watt

S4368 CF26DT/827

Packing: 50/Master,
Individually Sleeved

Quad

22 Watt

S6020 FDL22LE/D

S6021 FDL22EX/D

28 Watt

S6022 FDL28LE/D

S6023 FDL28EX/D

Packing: 50/Master,
Individually Sleeved

Dulux-L

18 Watt

S6772 CF18DF/830

S6773 CF18DF/841

24 Watt

S6774 CF24DF/830

S6775 CF24DF/841

36 Watt

S6776 CF36DF/830

S6777 CF36DF/841

Packing: 10/Master,
Individually Sleeved

Color Reference Guide

830 = 3000K Soft White

835 = 3500K Neutral

841 = 4100K Cool White

Not Shown Actual Size

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Description | Avg. Rated Hours | Lumens | Length | Pack. Type | Mst. Ctn./ Inner Pack |
|-------|-----------|---------|-----------------|------------|-------------|------------------|--------|--------|------------|-----------------------|
| 22 | T5 | GX32D-2 | S6020 | FDL22LE/D | 2800K 84CRI | 10000 | 1200 | 6.0" | Sleeve | 50 |
| 22 | T5 | GX32D-2 | S6021 | FDL22EX/D | 5000K 84CRI | 10000 | 1200 | 6.0" | Sleeve | 50 |
| 28 | T5 | GX32D-3 | S6022 | FDL28LE/D | 2800K 84CRI | 10000 | 1600 | 6.8" | Sleeve | 50 |
| 28 | T5 | GX32D-3 | S6023 | FDL28EX/D | 5000K 84CRI | 10000 | 1600 | 6.8" | Sleeve | 50 |
| 18 | T4 | GX24D-2 | S4367 | CF18DT/827 | 2700K 82CRI | 12000 | 1200 | 4.8" | Box | 50 |
| 26 | T4 | GX24D-3 | S4368 | CF26DT/827 | 2700K 82CRI | 12000 | 1800 | 5.4" | Box | 50 |
| 18 | T5 | 2G10 | S6772 | CF18DF/830 | 3000K 82CRI | 10000 | 1100 | 4.8" | Sleeve | 10 |
| 18 | T5 | 2G10 | S6773 | CF18DF/841 | 4100K 82CRI | 10000 | 1100 | 4.8" | Sleeve | 10 |
| 24 | T5 | 2G10 | S6774 | CF24DF/830 | 3000K 82CRI | 10000 | 1700 | 6.7" | Sleeve | 10 |
| 24 | T5 | 2G10 | S6775 | CF24DF/841 | 4100K 82CRI | 10000 | 1700 | 6.7" | Sleeve | 10 |
| 36 | T5 | 2G10 | S6776 | CF36DF/830 | 3000K 82CRI | 10000 | 2800 | 8.5" | Sleeve | 10 |
| 36 | T5 | 2G10 | S6777 | CF36DF/841 | 4100K 82CRI | 10000 | 2800 | 8.5" | Sleeve | 10 |

Compact Fluorescent



Mini Spirals

Not Shown Actual Size



Mini Spiral



**Mini Spiral
(Candelabra Base)**

MINI SPIRALS Their petite size and high lumen output have made this series the CFL of choice. These minis are suitable for many applications such as, table lamps, wall sconces, chandeliers with shades and task lighting with reflectors.

- 2700K, 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified*

| Watts | Base | Satco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | Length | Mst.Ctn./Inner Pack |
|-------------|-----------|-----------------|------------|-------------|------------------|-------|--------|-----|--------|---------------------|
| 5 | E26/Med. | S6298 | EFMSP5/27 | 2700K | 10000 | 120 | 250 | 82 | 4.06" | 6/24 Box |
| 9 | E26/Med. | S6200* | EFMSP9/30 | 3000K | 10000 | 120 | 500 | 82 | 4.45" | 6/24 Blister |
| 11 | E26/Med. | S6201* | EFMSP11/30 | 3000K | 6000 | 120 | 550 | 82 | 4.76" | 6/24 Blister |
| 13 | E26/Med. | S6202* | EFMSP13/30 | 3000K | 10000 | 120 | 800 | 82 | 4.96" | 6/24 Blister |
| 15 | E26/Med. | S6203* | EFMSP15/30 | 3000K | 10000 | 120 | 900 | 82 | 4.80" | 6/24 Blister |
| 18 | E26/Med. | S6243* | EFMSP18/30 | 3000K | 10000 | 120 | 1100 | 82 | 5.28" | 6/24 Blister |
| 26 | E26/Med. | S6204 | EFMSP26/30 | 3000K | 10000 | 120 | 1600 | 82 | 5.94" | 6/24 Blister |
| 13 | E26/Med. | S6223 | EFMSP13/50 | 5000K | 10000 | 120 | 800 | 82 | 4.96" | 6/24 Blister |
| 15 | E26/Med. | S6224 | EFMSP15/50 | 5000K | 10000 | 120 | 900 | 82 | 4.80" | 6/24 Blister |
| 26 | E26/Med. | S6225 | EFMSP26/50 | 5000K | 10000 | 120 | 1600 | 82 | 5.94" | 6/24 Blister |
| 5 | E12/Cand. | S6297 | EFMSP5/27 | 2700K | 10000 | 120 | 250 | 82 | 4.13" | 6/24 Box |
| 9 | E12/Cand. | S6251 | EFMSP9/30 | 3000K | 10000 | 120 | 500 | 82 | 4.45" | 6/24 Blister |
| 11 | E12/Cand. | S6252 | EFMSP11/30 | 3000K | 6000 | 120 | 550 | 82 | 4.76" | 6/24 Blister |
| 13 | E12/Cand. | S6253 | EFMSP13/30 | 3000K | 10000 | 120 | 800 | 82 | 4.96" | 6/24 Blister |
| 230V | | | | | | | | | | |
| 13 | E27/Med. | S6247 | EFMSP13/50 | 5000K | 10000 | 230 | 800 | 82 | 4.96" | 6/24 Blister |
| 26 | E27/Med. | S6248 | EFMSP26/50 | 5000K | 10000 | 230 | 1600 | 82 | 5.94" | 6/24 Blister |

*Energy Star Certified

fluorescent lamps



3-Way Spiral



Dimmable Spiral



Standard Spiral

- Dimmable & 3-Way Models
- 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified*



STANDARD SPIRALS Our new line of full size spiral lamps now feature a 23 watt dimmable model and our new 12/20/26 watt 3-way CFL. Other choices include lamps available in wattages from 15 to 32 watts in two color temperatures.

| Watts | Base | Satco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | Length | Mst.Ctn./ Inner Pack |
|----------|----------|-----------------|-------------------|-------------|------------------|-------|---------------|-----|--------|----------------------|
| 15 | E26/Med. | S6205* | EFSP15/30 | 3000K | 6000 | 120 | 900 | 82 | 5.35" | 6/24 Blister |
| 20 | E26/Med. | S6206* | EFSP20/30 | 3000K | 6000 | 120 | 1200 | 82 | 5.67" | 6/24 Blister |
| 23 | E26/Med. | S6207* | EFSP23/30 | 3000K | 6000 | 120 | 1380 | 82 | 6.02" | 6/24 Blister |
| 26 | E26/Med. | S6209* | EFSP26/30 | 3000K | 6000 | 120 | 1600 | 82 | 6.14" | 6/24 Blister |
| 32 | E26/Med. | S6210* | EFSP32/30 | 3000K | 6000 | 120 | 1920 | 82 | 6.73" | 6/24 Blister |
| 15 | E26/Med. | S6226 | EFSP15/50 | 5000K | 6000 | 120 | 900 | 82 | 5.35" | 6/24 Blister |
| 20 | E26/Med. | S6227 | EFSP20/50 | 5000K | 6000 | 120 | 1200 | 82 | 5.67" | 6/24 Blister |
| 23 | E26/Med. | S6228 | EFSP23/50 | 5000K | 6000 | 120 | 1380 | 82 | 6.02" | 6/24 Blister |
| 26 | E26/Med. | S6229 | EFSP26/50 | 5000K | 6000 | 120 | 1600 | 82 | 6.14" | 6/24 Blister |
| 32 | E26/Med. | S6240 | EFSP32/50 | 5000K | 6000 | 120 | 1920 | 82 | 6.73" | 6/24 Blister |
| 12/20/26 | E26/Med. | S6211* | EFSP12-26/30/3WAY | 3000K | 6000 | 120 | 660/1200/1600 | 82 | 6.02" | 6/24 Blister |
| 23 | E26/Med. | S6212* | EFSP23/30/DIM | 3000K | 6000 | 120 | 1380 | 82 | 6.02" | 6/24 Blister |

*Energy Star Certified

Compact Fluorescent R20 Reflectors



6000 Hours

Not Shown Actual Size



R20

Reflector



R20

Reflector
(Long)

R E F L E C T O R S
Compact, sleek and efficient describe this latest series of energy saving reflectors. Technology has enabled us to develop these 21st century products; their performance and appearance rival their incandescent counterparts.

- 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified*



| Watts | Base | Salco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | Length | Mst. Ctn./ Inner Pack |
|-------------|----------|-----------------|-------------|-------------|------------------|-------|--------|-----|--------|-----------------------|
| 5 | E26/Med. | S6244* | EFR205/30 | 3000K | 6000 | 120 | 260 | 82 | 4.21" | 6/24 Blister |
| 11 | E26/Med. | S6245 | EFR20L11/30 | 3000K | 6000 | 120 | 330 | 82 | 4.96" | 6/24 Blister |
| 230V | | | | | | | | | | |
| 11 | E27/Med. | S6249 | EFR20L11/50 | 5000K | 6000 | 230 | 330 | 82 | 4.96" | 6/24 Blister |

fluorescent lamps



Compact Fluorescent **R30 & BR38** Reflectors

6000 Hours



Not Shown Actual Size



| | | | |
|---------------------|--------------------------|---------------------------|------------------|
| WET LOCATION | BR38 | R30 | R30 |
| | Outdoor Reflector | Dimmable Reflector | Reflector |

REFLECTORS Our new 23 watt PAR38 reflector delivers a high lumen punch of light while being Energy Star certified and U.L. listed for wet location applications. Also new is our "Dimmable" R30 reflector.

- 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified*



| Watts | Base | Satco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | Length | Mst.Ctn./ Inner Pack |
|-------|----------|-----------------|----------------|-------------|------------------|-------|--------|-----|--------|----------------------|
| 15 | E26/Med. | S6213* | EFR3015/30 | 3000K | 6000 | 120 | 550 | 82 | 5.39" | 6/24 Blister |
| 15 | E26/Med. | S6255* | EFR3015/DIM/30 | 3000K | 6000 | 120 | 525 | 82 | 6.10" | 6/24 Blister |
| 23 | E26/Med. | S6215* | EFPAR3823/30 | 3000K | 6000 | 120 | 960 | 82 | 6.50" | 6/24 Blister |

*Energy Star Certified

fluorescent lamps

Compact Fluorescent



R40 Reflectors

6000 Hours

Not Shown Actual Size



R40

Reflector

R40

Dimmable
Reflector

R E F L E C T O R S
Compact, sleek and efficient describe this latest series of energy saving reflectors.

- 3000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified*



| Watts | Base | Satco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | Length | Mst.Ctn./ Inner Pack |
|-------|----------|-----------------|----------------|-------------|------------------|-------|--------|-----|--------|----------------------|
| 23 | E26/Med. | S6214* | EFR4023/30 | 3000K | 6000 | 120 | 920 | 82 | 6.50" | 6/24 Blister |
| 23 | E26/Med. | S6256 | EFR4023/DIM/30 | 3000K | 6000 | 120 | 920 | 82 | 7.00" | 6/24 Blister |

*Energy Star Certified

fluorescent lamps



Compact Fluorescent

6000 Hours

A Type Household Bulbs



Not Shown Actual Size

| | | | |
|----------------|----------------|----------------|----------------|
| 15W | 11W | 9W | 7W |
| Household Bulb | Household Bulb | Household Bulb | Household Bulb |

A-TYPE BULBS This collection provides an aesthetic value to these functional products. The compact A-type lamp delivers impressive lumen performance for an enclosed lamp.

- 3000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified*



| Watts | Base | Satco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | Length | Mst.Ctn./ Inner Pack |
|-------|----------|-----------------|------------|-------------|------------------|-------|--------|-----|--------|----------------------|
| 7 | E26/Med. | S6233* | EF7A19/30 | 3000K | 6000 | 120 | 300 | 82 | 4.54" | 6/24 Blister |
| 9 | E26/Med. | S6239* | EF9A19/30 | 3000K | 6000 | 120 | 450 | 82 | 4.61" | 6/24 Blister |
| 11 | E26/Med. | S6246* | EF11A19/30 | 3000K | 6000 | 120 | 540 | 82 | 4.96" | 6/24 Blister |
| 15 | E26/Med. | S6216* | EF15A19/30 | 3000K | 6000 | 120 | 720 | 82 | 5.39" | 6/24 Blister |

*Energy Star Certified

fluorescent lamps

Compact Fluorescent Bulbs



fluorescent lamps



- 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified*



Not Shown Actual Size

| Watts | Base | Salco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | Length | Mst. Ctn./ Inner Pack |
|-------|-----------|-----------------|--------------|-------------|------------------|-------|--------|-----|--------|-----------------------|
| 3 | E12/Cand. | S6219 | EFTOR3/30 | 3000K | 6000 | 120 | 120 | 82 | 4.96" | 6/24 Blister |
| 7 | E12/Cand. | S6220 | EFTOR7/30 | 3000K | 6000 | 120 | 280 | 82 | 4.96" | 6/24 Blister |
| 3 | E26/Med. | S6221 | EFTOR3/30 | 3000K | 6000 | 120 | 120 | 82 | 4.96" | 6/24 Blister |
| 7 | E26/Med. | S6222* | EFTOR7/30 | 3000K | 6000 | 120 | 280 | 82 | 4.96" | 6/24 Blister |
| 15 | E26/Med. | S6217 | EFT15/30 | 3000K | 6000 | 120 | 720 | 82 | 5.51" | 6/24 Blister |
| 15 | E26/Med. | S6241 | EFT15/50 | 5000K | 6000 | 120 | 720 | 82 | 5.51" | 6/24 Blister |
| 15 | E26/Med. | S6218* | EFG15/30 | 3000K | 6000 | 120 | 720 | 82 | 5.39" | 6/24 Blister |
| 15 | E26/Med. | S6242 | EFG15/50 | 5000K | 6000 | 120 | 720 | 82 | 5.39" | 6/24 Blister |
| 15 | E27/Med. | S6250 | EFG15/50/230 | 5000K | 6000 | 230 | 720 | 82 | 5.39" | 6/24 Blister |

*Energy Star Certified



23W
Spiral Bulb

with Dual Photocells



Mini Spiral

Bug Light

| Watts | Base | Satco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | Length | Mst.Ctn./ Inner Pack |
|-------|----------|-----------------|-------------------|-------------|------------------|-------|--------|-----|--------|----------------------|
| 15 | E26/Med. | S6254 | EFMSP15/BUG | N/A | 10000 | 120 | N/A | N/A | 4.88" | 6/24 Blister |
| 23 | E26/Med. | S6257 | EF23/SPL/PHOTO/30 | 3000K | 6000 | 120 | 1060 | >75 | 2.5" | 6/24 Blister |

Not Shown Actual Size

Fluorescent *Specialty* Lamps



fluorescent lamps



22W

Circline Style

- 3000K & 6500K Color Temperatures
- 10000 Hours

Not Shown Actual Size

| Watts | Base | Satco Order No. | Lamp Code | Color Temp. | Avg. Rated Hours | Volts | Lumens | CRI | M.O.L. | Mst.Ctn./ Inner Pack |
|-------|----------|-----------------|--------------|-------------|------------------|-------|--------|-----|--------|----------------------|
| 22 | E26/Med. | S6259 | EF/FC8/T9/WW | 3000K | 10000 | 120 | 1060 | 52 | 3" | 6/24 Blister |
| 22 | E26/Med. | S6261 | EF/FC8/T9/D | 6500K | 10000 | 120 | 1060 | 76 | 3" | 6/24 Blister |

Metal Halide

Mogul Base



BT28

ED28

BT37

ED37

BT56

- Standard (Probe) Start
- Enclosed Rated
- Universal – Varied Burning Position



ED28

ED37

BT56

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | ANSI | Finish | Color Temp | CRI | Average Rated Hours | Initial Lumens | Operating Position | M.O.L. | Case |
|-------|-----------|-------|-----------------|----------------|-------|--------|------------|-----|---------------------|----------------|--------------------|--------|------|
| 175 | BT28 | Mogul | S4829 | MH175/U | M57/E | Clear | 4000K | 65 | 10000 | 14000 | Univ. | 8 5/16 | 6 |
| 175 | ED28 | Mogul | S4830 | MH175/C/U | M57/E | Coated | 3700K | 70 | 10000 | 13300 | Univ. | 8 5/16 | 12 |
| 250 | BT28 | Mogul | S4831 | MH250/U | M58/E | Clear | 4000K | 65 | 10000 | 21000 | Univ. | 8 5/16 | 6 |
| 250 | ED28 | Mogul | S4832 | MH250/C/U | M58/E | Coated | 3700K | 70 | 10000 | 20000 | Univ. | 8 5/16 | 12 |
| 400 | BT37 | Mogul | S4833 | MH400/U | M59/E | Clear | 4000K | 65 | 20000 | 36000 | Univ. | 11 1/2 | 6 |
| 400 | ED37 | Mogul | S4834 | MH400/C/U | M59/E | Coated | 3700K | 70 | 20000 | 34000 | Univ. | 11 1/2 | 6 |
| 400 | ED28 | Mogul | S4843 | MH400/U/ED28 | M59/E | Clear | 4000K | 65 | 20000 | 36000 | Univ. | 8 5/16 | 12 |
| 400 | ED28 | Mogul | S4844 | MH400/C/U/ED28 | M59/E | Coated | 3700K | 70 | 20000 | 34000 | Univ. | 8 5/16 | 12 |
| 1000 | BT56 | Mogul | S4835 | MH1000/U | M47/E | Clear | 4000K | 65 | 18000 | 110000 | Univ. | 15 3/8 | 6 |
| 1000 | BT56 | Mogul | S4836 | MH1000/C/U | M47/E | Coated | 3700K | 70 | 12000 | 105000 | Univ. | 15 3/8 | 6 |
| 1000 | BT37 | Mogul | S4845 | MH1000/U/BT37 | M47/E | Clear | 4000K | 65 | 12000 | 110000 | Univ. | 11 1/2 | 6 |
| 1500 | BT56 | Mogul | S4837 | MH1500/HBU | M48/E | Clear | 3400K | 65 | 3000 | 161000 | BU 105 | 15 3/8 | 6 |
| 1500 | BT56 | Mogul | S4839 | MH1500/U/XL | M48/E | Clear | 4000K | 65 | 6000 | 170000 | Univ. | 15 3/8 | 6 |

*Hours and lumens are based on vertical burning position • When used horizontally, hours and lumens are reduced.

Metal Halide

Medium Base



ED17
Clear

ED17
Coated

For Use in Enclosed Rated Fixtures •

PULSE START

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | ANSI | Finish | Color Temp. | CRI | Average Rated Hours | Initial Lumens | Operating Position | M.O.L. | Case |
|-------|-----------|------|-----------------|------------------|--------|--------|-------------|-----|---------------------|----------------|--------------------|--------|------|
| 50 | ED17 | Med. | S4854 | MH50/U/MED/PS | M110/E | Clear | 4000K | 65 | 10000 | 3400 | Univ. | 5 7/16 | 12 |
| 50 | ED17 | Med. | S4855 | MH50/C/U/MED/PS | M110/E | Coated | 3700K | 70 | 10000 | 3200 | Univ. | 5 7/16 | 12 |
| 70 | ED17 | Med. | S4856 | MH70/U/MED/PS | M98/E | Clear | 4000K | 65 | 10000 | 5600 | Univ. | 5 7/16 | 12 |
| 70 | ED17 | Med. | S4857 | MH70/C/U/MED/PS | M98/E | Coated | 3700K | 70 | 10000 | 5300 | Univ. | 5 7/16 | 12 |
| 100 | ED17 | Med. | S4858 | MH100/U/MED/PS | M90/E | Clear | 4000K | 65 | 10000 | 9000 | Univ. | 5 7/16 | 12 |
| 100 | ED17 | Med. | S4859 | MH100/C/U/MED/PS | M90/E | Coated | 3700K | 70 | 10000 | 8500 | Univ. | 5 7/16 | 12 |
| 150 | ED17 | Med. | S4860 | MH150/U/MED/PS | M102/E | Clear | 4000K | 65 | 10000 | 14000 | Univ. | 5 7/16 | 12 |
| 150 | ED17 | Med. | S4861 | MH150/C/U/MED/PS | M102/E | Coated | 3700K | 70 | 10000 | 13300 | Univ. | 5 7/16 | 12 |

STANDARD PROBE START

| | | | | | | | | | | | | | |
|-----|------|------|--------------|---------------|-------|--------|-------|----|-------|-------|-------|--------|----|
| 175 | ED17 | Med. | S4862 | MH175/U/MED | M57/E | Clear | 4000K | 65 | 10000 | 14000 | Univ. | 5 7/16 | 12 |
| 175 | ED17 | Med. | S4863 | MH175/C/U/MED | M57/E | Coated | 3700K | 70 | 10000 | 13300 | Univ. | 5 7/16 | 12 |



EDX17
Clear

EDX17
Coated

For Use in Open or Enclosed Rated Fixtures •

PULSE START

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | ANSI | Finish | Color Temp. | CRI | Avg. Rated Hours | Initial Lumens | Operating Position | Case |
|-------|-----------|------|-----------------|--------------------|--------|--------|-------------|-----|------------------|----------------|--------------------|------|
| 50 | EDX17 | Med. | S4846 | MP50/U/UVS/3K/PS | M110/O | Clear | 3000K | 65 | 10000 | 3200 | Univ. | 12 |
| 50 | EDX17 | Med. | S4847 | MP50/C/U/UVS/3K/PS | M110/O | Coated | 3200K | 70 | 10000 | 3000 | Univ. | 12 |
| 70 | EDX17 | Med. | S4848 | MP70/U/UVS/PS | M98/O | Clear | 4000K | 65 | 10000 | 5300 | Univ. | 12 |
| 70 | EDX17 | Med. | S4849 | MP70/C/U/UVS/PS | M98/O | Coated | 3700K | 70 | 10000 | 5000 | Univ. | 12 |
| 100 | EDX17 | Med. | S4850 | MP100/U/UVS/PS | M90/O | Clear | 4000K | 65 | 10000 | 8500 | Univ. | 12 |
| 100 | EDX17 | Med. | S4851 | MP100/C/U/UVS/PS | M90/O | Coated | 3700K | 70 | 10000 | 8100 | Univ. | 12 |
| 150 | EDX17 | Med. | S4852 | MP150/U/UVS/PS | M102/O | Clear | 4000K | 65 | 10000 | 13300 | Univ. | 12 |
| 150 | EDX17 | Med. | S4853 | MP150/C/U/UVS/PS | M102/O | Coated | 3700K | 70 | 10000 | 12600 | Univ. | 12 |

STANDARD PROBE START

| | | | | | | | | | | | | |
|-----|-------|------|--------------|-------------------|-------|-------|-------|----|-------|-------|---------|----|
| 175 | EDX17 | Med. | S4828 | MP175/BU-ONLY/MED | M57/O | Clear | 3600K | 65 | 10000 | 14400 | Base Up | 20 |
|-----|-------|------|--------------|-------------------|-------|-------|-------|----|-------|-------|---------|----|

*Hours and lumens are based on vertical burning position • When used horizontally, hours and lumens are reduced.

Metal Halide

Medium Base



ED17
Clear

ED17
Coated

For Use in Enclosed Rated Fixtures •

PULSE START

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | ANSI | Finish | Color Temp. | CRI | Average Rated Hours | Initial Lumens | Operating Position | M.O.L. | Case |
|-------|-----------|------|-----------------|------------------|--------|--------|-------------|-----|---------------------|----------------|--------------------|--------|------|
| 50 | ED17 | Med. | S4854 | MH50/U/MED/PS | M110/E | Clear | 4000K | 65 | 10000 | 3400 | Univ. | 5 7/16 | 12 |
| 50 | ED17 | Med. | S4855 | MH50/C/U/MED/PS | M110/E | Coated | 3700K | 70 | 10000 | 3200 | Univ. | 5 7/16 | 12 |
| 70 | ED17 | Med. | S4856 | MH70/U/MED/PS | M98/E | Clear | 4000K | 65 | 10000 | 5600 | Univ. | 5 7/16 | 12 |
| 70 | ED17 | Med. | S4857 | MH70/C/U/MED/PS | M98/E | Coated | 3700K | 70 | 10000 | 5300 | Univ. | 5 7/16 | 12 |
| 100 | ED17 | Med. | S4858 | MH100/U/MED/PS | M90/E | Clear | 4000K | 65 | 10000 | 9000 | Univ. | 5 7/16 | 12 |
| 100 | ED17 | Med. | S4859 | MH100/C/U/MED/PS | M90/E | Coated | 3700K | 70 | 10000 | 8500 | Univ. | 5 7/16 | 12 |
| 150 | ED17 | Med. | S4860 | MH150/U/MED/PS | M102/E | Clear | 4000K | 65 | 10000 | 14000 | Univ. | 5 7/16 | 12 |
| 150 | ED17 | Med. | S4861 | MH150/C/U/MED/PS | M102/E | Coated | 3700K | 70 | 10000 | 13300 | Univ. | 5 7/16 | 12 |

STANDARD PROBE START

| | | | | | | | | | | | | | |
|-----|------|------|--------------|---------------|-------|--------|-------|----|-------|-------|-------|--------|----|
| 175 | ED17 | Med. | S4862 | MH175/U/MED | M57/E | Clear | 4000K | 65 | 10000 | 14000 | Univ. | 5 7/16 | 12 |
| 175 | ED17 | Med. | S4863 | MH175/C/U/MED | M57/E | Coated | 3700K | 70 | 10000 | 13300 | Univ. | 5 7/16 | 12 |



EDX17
Clear

EDX17
Coated

For Use in Open or Enclosed Rated Fixtures •

PULSE START

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | ANSI | Finish | Color Temp. | CRI | Avg. Rated Hours | Initial Lumens | Operating Position | Case |
|-------|-----------|------|-----------------|--------------------|--------|--------|-------------|-----|------------------|----------------|--------------------|------|
| 50 | EDX17 | Med. | S4846 | MP50/U/UVS/3K/PS | M110/O | Clear | 3000K | 65 | 10000 | 3200 | Univ. | 12 |
| 50 | EDX17 | Med. | S4847 | MP50/C/U/UVS/3K/PS | M110/O | Coated | 3200K | 70 | 10000 | 3000 | Univ. | 12 |
| 70 | EDX17 | Med. | S4848 | MP70/U/UVS/PS | M98/O | Clear | 4000K | 65 | 10000 | 5300 | Univ. | 12 |
| 70 | EDX17 | Med. | S4849 | MP70/C/U/UVS/PS | M98/O | Coated | 3700K | 70 | 10000 | 5000 | Univ. | 12 |
| 100 | EDX17 | Med. | S4850 | MP100/U/UVS/PS | M90/O | Clear | 4000K | 65 | 10000 | 8500 | Univ. | 12 |
| 100 | EDX17 | Med. | S4851 | MP100/C/U/UVS/PS | M90/O | Coated | 3700K | 70 | 10000 | 8100 | Univ. | 12 |
| 150 | EDX17 | Med. | S4852 | MP150/U/UVS/PS | M102/O | Clear | 4000K | 65 | 10000 | 13300 | Univ. | 12 |
| 150 | EDX17 | Med. | S4853 | MP150/C/U/UVS/PS | M102/O | Coated | 3700K | 70 | 10000 | 12600 | Univ. | 12 |

STANDARD PROBE START

| | | | | | | | | | | | | |
|-----|-------|------|--------------|-------------------|-------|-------|-------|----|-------|-------|---------|----|
| 175 | EDX17 | Med. | S4828 | MP175/BU-ONLY/MED | M57/O | Clear | 3600K | 65 | 10000 | 14400 | Base Up | 20 |
|-----|-------|------|--------------|-------------------|-------|-------|-------|----|-------|-------|---------|----|

*Hours and lumens are based on vertical burning position • When used horizontally, hours and lumens are reduced.

Metal Halide

- Mogul Base
- Standard (Probe) Start
- Enclosed Rated
- Specified Burning Position



HID lamps

| Watts | Bulb Type | Base* | Salco Order No. | Lamp Code | ANSI | Finish | Color Temp. | CRI | Avg. Rated Hours | Initial Lumens | Operating Position | MOL | Case |
|-------|-----------|-------|-----------------|------------------|-------|--------|-------------|-----|------------------|----------------|--------------------|--------|------|
| 175 | ED28 | E39 | S4271 | MS175/BU | M57/E | Clear | 4000K | 65 | 10000 | 15000 | BU±15° | 8 5/16 | 12 |
| 175 | ED28 | EP39 | S4272 | MS175/HOR | M57/E | Clear | 4000K | 65 | 10000 | 15000 | HOR± 45° | 8 5/16 | 12 |
| 175 | T15 | E39 | S4840 | MH175/U/T15 | M57/E | Clear | 4000K | 65 | 10000 | 14000 | Univ. | 8 5/16 | 12 |
| 250 | ED28 | E39 | S4273 | MS250/BU | M58/E | Clear | 4000K | 65 | 10000 | 23000 | BU±15° | 8 5/16 | 12 |
| 250 | ED28 | E39 | S4274 | MS250/C/BU | M58/E | Coated | 3700K | 70 | 10000 | 22000 | BU±15° | 8 5/16 | 12 |
| 250 | ED28 | EP39 | S4275 | MS250/HOR | M58/E | Clear | 4000K | 65 | 10000 | 23000 | HOR± 45° | 8 5/16 | 12 |
| 250 | T15 | E39 | S4841 | MH250/U/T15 | M58/E | Clear | 4000K | 65 | 10000 | 21000 | Univ. | 8 5/16 | 12 |
| 250 | T15 | EP39 | S4868 | MS250/HOR/T15/3K | M58/E | Clear | 3200K | 65 | 10000 | 21000 | HOR± 45° | 8 5/16 | 12 |
| 400 | ED37 | E39 | S4276 | MS400/BU | M59/E | Clear | 4000K | 65 | 20000 | 40000 | BU±15° | 11 1/2 | 6 |
| 400 | ED37 | E39 | S4277 | MS400/C/BU | M59/E | Coated | 3700K | 70 | 20000 | 38000 | BU±15° | 11 1/2 | 6 |
| 400 | ED28 | E39 | S4278 | MS400/BU/ED28 | M59/E | Clear | 4000K | 65 | 20000 | 40000 | BU±15° | 8 5/16 | 12 |
| 400 | ED37 | EP39 | S4279 | MS400/HOR | M59/E | Clear | 4000K | 65 | 20000 | 40000 | HOR± 45° | 11 1/2 | 6 |
| 400 | ED37 | EP39 | S4280 | MS400/C/HOR | M59/E | Coated | 3700K | 70 | 20000 | 38000 | HOR± 45° | 11 1/2 | 6 |
| 400 | ED28 | EP39 | S4281 | MS400/HOR/ED28 | M59/E | Clear | 4000K | 65 | 20000 | 40000 | HOR± 45° | 8 5/16 | 12 |
| 400 | T15 | EP39 | S4842 | MH400/HBU/T15 | M59/E | Clear | 4000K | 65 | 15000 | 36000 | BU 90 | 9 3/4 | 12 |
| 400 | T15 | EP39 | S4282 | MS400/HOR/T15/3K | M59/E | Clear | 3200K | 65 | 15000 | 38000 | HOR± 45° | 9 3/4 | 12 |
| 1000 | BT56 | E39 | S4283 | MS1000/BU | M47/E | Clear | 4000K | 65 | 12000 | 115000 | BU± 15° | 15 3/8 | 6 |

*Base Information

E39 = Standard Mogul Base

EP39 = Position Oriented Mogul Base

Pulse Start Metal Halide



- Enclosed Rated •
- Specified •
- Burning Position

ED37
Coated / Clear

ED28
Coated / Clear

ED17
Coated / Clear

| Watts | Bulb Type | Base* | Salco Order No. | Lamp Code | ANSI | Finish | Color Temp. | CRI | Avg. Rated Hours | Initial Lumens | Operating Position | MOL | Case |
|-------|-----------|-------|-----------------|-------------------|--------|--------|-------------|-----|------------------|----------------|--------------------|--------|------|
| 175 | ED17 | Med | S4234 | MS175/BU/MED/PS | M152/E | Clear | 4000K | 65 | 15000 | 17500 | BU±15° | 5 7/16 | 12 |
| 175 | ED17 | Med | S4235 | MS175/C/BU/MED/PS | M152/E | Coated | 3700K | 70 | 15000 | 16600 | BU±15° | 5 7/16 | 12 |
| 175 | ED28 | Mog | S4236 | MS175/BU/PS | M152/E | Clear | 4000K | 65 | 15000 | 17500 | BU±15° | 8 5/16 | 12 |
| 175 | ED28 | Mog | S4237 | MS175/C/BU/PS | M152/E | Coated | 3700K | 70 | 15000 | 16600 | BU±15° | 8 5/16 | 12 |
| 200 | ED17 | Med | S4238 | MS200/BU/MED/PS | M136/E | Clear | 4000K | 65 | 12000 | 21000 | BU±15° | 5 7/16 | 12 |
| 200 | ED28 | Mog | S4291 | MS200/V/PS | M136/E | Clear | 4000K | 65 | 15000 | 21000 | Vert±15° | 8 5/16 | 12 |
| 250 | ED28 | Mog | S4239 | MS250/V/PS | M153/E | Clear | 4000K | 65 | 15000 | 25000 | Vert±15° | 8 5/16 | 12 |
| 250 | ED28 | Mog | S4240 | MS250/H75/PS | M153/E | Clear | 4000K | 65 | 15000 | 22000 | Hor±5° | 8 5/16 | 12 |
| 320 | ED28 | Mog | S4241 | MS320/V/ED28/PS | M154/E | Clear | 4000K | 65 | 20000 | 33000 | Vert±15° | 8 5/16 | 12 |
| 320 | ED28 | Mog | S4242 | MS320/C/V/ED28/PS | M154/E | Coated | 3700K | 70 | 20000 | 31000 | Vert±15° | 8 5/16 | 12 |
| 350 | ED37 | Mog | S4243 | MS350/V/PS | M131/E | Clear | 4000K | 65 | 20000 | 37000 | Vert±15° | 11 1/2 | 6 |
| 350 | ED37 | Mog | S4244 | MS350/C/V/PS | M131/E | Coated | 3700K | 70 | 20000 | 35000 | Vert±15° | 11 1/2 | 6 |
| 400 | ED37 | Mog | S4245 | MS400/V/PS | M155/E | Clear | 4000K | 65 | 20000 | 44000 | Vert±15° | 11 1/2 | 6 |
| 400 | ED37 | Mog | S4246 | MS400/C/V/PS | M155/E | Coated | 3700K | 70 | 20000 | 42000 | Vert±15° | 11 1/2 | 6 |
| 400 | ED28 | Mog | S4247 | MS400/V/ED28/PS | M155/E | Clear | 4000K | 65 | 20000 | 44000 | Vert±15° | 8 5/16 | 12 |
| 400 | ED28 | Mog | S4248 | MS400/C/V/ED28/PS | M155/E | Coated | 3700K | 70 | 20000 | 42000 | Vert±15° | 8 5/16 | 12 |
| 400 | ED37 | Mog | S4249 | MS400/H75/PS | M155/E | Clear | 4000K | 65 | 20000 | 40000 | Hor±75° | 11 1/2 | 6 |
| 400 | ED28 | Mog | S4250 | MS400/H75/ED28/PS | M155/E | Clear | 4000K | 65 | 20000 | 40000 | Hor±75° | 8 5/16 | 12 |



ED37
Clear / Coated

ED28
Clear / Coated

- Open Rated •
- UV Shield •
- Specified Burning Position •
- Mogul Base •

| Watts | Bulb Type | Base* | Salco Order No. | Lamp Code | ANSI | Finish | Color Temp. | CRI | Avg. Rated Hours | Initial Lumens | Operating Position | MOL | Case |
|-------|-----------|----------|-----------------|------------------------|--------|--------|-------------|-----|------------------|----------------|--------------------|--------|------|
| 200 | ED28 | Mog EX39 | S4251 | MP200/V/UVS/PS | M136/O | Clear | 4000K | 65 | 15000 | 20000 | Vert±15° | 8 5/16 | 12 |
| 250 | ED28 | Mog EX39 | S4252 | MP250/BU/UVS/PS | M153/O | Clear | 4000K | 65 | 15000 | 23800 | BU±15° | 8 5/16 | 12 |
| 320 | ED28 | Mog EX39 | S4253 | MP320/BU/ED28/UVS/PS | M154/O | Clear | 4000K | 65 | 20000 | 31000 | BU±15° | 8 5/16 | 12 |
| 320 | ED28 | Mog EX39 | S4254 | MP320/C/BU/ED28/UVS/PS | M154/O | Coated | 3700K | 70 | 20000 | 29000 | BU±15° | 8 5/16 | 12 |
| 320 | ED37 | Mog EX39 | S4255 | MP320/BU/ED37/UVS/PS | M154/O | Clear | 4000K | 65 | 20000 | 31000 | BU±15° | 11 1/2 | 6 |
| 350 | ED37 | Mog EX39 | S4256 | MP350/V/UVS/PS | M131/O | Clear | 4000K | 65 | 20000 | 35000 | Vert±15° | 11 1/2 | 6 |
| 350 | ED37 | Mog EX39 | S4257 | MP350/C/V/UVS/PS | M131/O | Coated | 3700K | 70 | 20000 | 33000 | Vert±15° | 11 1/2 | 6 |
| 400 | ED37 | Mog EX39 | S4258 | MP400/BU/UVS/PS | M155/O | Clear | 4000K | 65 | 20000 | 42000 | BU±15° | 11 1/2 | 6 |
| 400 | ED37 | Mog EX39 | S4259 | MP400/C/BU/UVS/PS | M155/O | Coated | 3700K | 70 | 20000 | 40000 | BU±15° | 11 1/2 | 6 |

HID lamps

Metal Halide

- Ceramic Technology
- Par Type
- Open Rated
- Universal – Burning Position
- Medium Base



PAR20

PAR30

PAR38

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | ANSI | Beam | Initial Lumens | CBCP | Color Temp | CRI | Avg. Life Hours | M.O.L. | Position | Case |
|-------|-----------|--------|-----------------|-------------------|------------|-----------|----------------|-------|------------|-----|-----------------|--------|-----------|------|
| 39 | PAR20 | Medium | S4284 | CDM35PAR20/M/SP | M130/O | Spot 10° | 2000 | 23000 | 3000K | 81 | 9000 | 3 3/4 | Universal | 12 |
| 39 | PAR20 | Medium | S4285 | CDM35PAR20/M/FL | M130/O | Flood 30° | 2000 | 5000 | 3000K | 81 | 9000 | 3 3/4 | Universal | 12 |
| 39 | PAR30L | Medium | S4876 | CDM35PAR30L/M/SP | M130/O | Spot 10° | 2000 | 44000 | 3000K | 81 | 9000 | 4 3/4 | Universa | 6 |
| 39 | PAR30L | Medium | S4877 | CDM35PAR30L/M/FL | M130/O | Flood 30° | 2000 | 7400 | 3000K | 81 | 9000 | 4 3/4 | Universal | 6 |
| 70 | PAR30L | Medium | S4878 | CDM70PAR30L/M/SP | M143/M98/O | Spot 10° | 4800 | 68000 | 3000K | 83 | 9000 | 4 3/4 | Universal | 6 |
| 70 | PAR30L | Medium | S4879 | CDM70PAR30L/M/FL | M143/M98/O | Flood 30° | 4800 | 10000 | 3000K | 83 | 9000 | 4 3/4 | Universal | 6 |
| 70 | PAR38 | Medium | S4897 | CDM70PAR38/SP/3K | M143/M98/O | Spot 10° | 4800 | 50000 | 3000K | 82 | 10000 | 5 7/6 | Universal | 12 |
| 70 | PAR38 | Medium | S4812 | CDM70PAR38/SP/4K | M143/M98/O | Spot 10° | 4200 | 42000 | 4000K | 92 | 10000 | 5 7/6 | Universal | 12 |
| 70 | PAR38 | Medium | S4898 | CDM70PAR38/FL/3K | M143/M98/O | Flood 30° | 4800 | 18000 | 3000K | 82 | 10000 | 5 7/6 | Universal | 12 |
| 70 | PAR38 | Medium | S4813 | CDM70PAR38/FL/4K | M143/M98/O | Flood 30° | 4200 | 16000 | 4000K | 92 | 10000 | 5 7/6 | Universal | 12 |
| 100 | PAR38 | Medium | S4888 | CDM100PAR38/SP/3K | M140/M90/O | Spot 10° | 6800 | 70000 | 3000K | 85 | 12500 | 5 7/6 | Universal | 12 |
| 100 | PAR38 | Medium | S4814 | CDM100PAR38/SP/4K | M140/M90/O | Spot 10° | 6000 | 54000 | 4000K | 93 | 10000 | 5 7/6 | Universal | 12 |
| 100 | PAR38 | Medium | S4889 | CDM100PAR38/FL/3K | M140/M90/O | Flood 30° | 6800 | 25000 | 3000K | 85 | 12500 | 5 7/6 | Universal | 12 |
| 100 | PAR38 | Medium | S4869 | CDM100PAR38/FL/4K | M140/M90/O | Flood 30° | 6000 | 20000 | 4000K | 93 | 10000 | 5 7/6 | Universal | 12 |

- R40 Reflector Type
- Enclosed rated
- Universal – Varied Burning Position
- Medium Base



R40

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | ANSI | Beam | Initial Lumens | CBCP | CCT(K) | C.R.I. | Avg. Life | M.O.L. | Operating Position | Case |
|-------|-----------|--------|-----------------|-----------------|-------|-----------|----------------|-------|--------|--------|-----------|--------|--------------------|------|
| 175 | R40 | Medium | S4260 | MH175W/U/R40/15 | M57/E | Spot 10° | n/a | 65000 | 4000K | 65 | 10000 | 6 1/2 | Universal | 6 |
| 175 | R40 | Medium | S4261 | MH175W/U/R40/70 | M57/E | Flood 70° | n/a | 6500 | 4000K | 65 | 10000 | 6 1/2 | Universal | 6 |

Metal Halide



70W/MH-DE



150W/MH-DE

- Double Ended Type
- Enclosed Rated

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Finish | ANSI | Avg. Rated Life | Initial Lumens | CCT(K) | CRI | M.O.L. | Operating Position | Case |
|-------|------------|------|-----------------|------------------|--------|------------|-----------------|----------------|--------|-----|--------|--------------------|------|
| 70 | DE Tubular | RSC | S4865 | MH-DE70/UVS/3K | Clear | M85/M98/E | 10000 | 5200 | 3000 | 70 | 4 7/16 | HOR±45° | 25 |
| 70 | DE Tubular | RSC | S4864 | MH-DE70/UVS/4K | Clear | M85/M98/E | 10000 | 5500 | 4200 | 65 | 4 7/16 | HOR±45° | 25 |
| 150 | DE Tubular | RSC | S4866 | MH-DE150/UVS/3K | Clear | M81/M102/E | 10000 | 12500 | 3000 | 70 | 5 7/16 | HOR±45° | 25 |
| 150 | DE Tubular | RSC | S4867 | MH-DE150/UVS/4K | Clear | M81/M102/E | 10000 | 12000 | 4200 | 65 | 5 7/16 | HOR±45° | 25 |
| 250 | DE Tubular | Fc2 | S4262 | MH-DE250W/3K/Fc2 | Clear | M80E | 10000 | 20000 | 3000 | 70 | 6 1/2 | HOR±45° | 25 |
| 250 | DE Tubular | Fc2 | S4263 | MH-DE250W/4K/Fc2 | Clear | M80E | 10000 | 20000 | 4200 | 70 | 6 1/2 | HOR±45° | 25 |



TD-6 - RX7



TD-7 - RX7



T-6
G12

T-4
G8.5

- Ceramic Technology
- Single Ended T Type
- Double Ended T Type
- Enclosed Rated
- Universal - Varied Burning Position

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Finish | ANSI | Avg. Rated Life | Initial Lumens | Color Temp | CRI | M.O.L. | Operating Position | Case |
|-------|------------|------|-----------------|---------------|--------|-----------------|-----------------|----------------|------------|-----|---------|--------------------|------|
| 39 | SE Tubular | G8.5 | S4286 | CDM35/TC/830 | Clear | M130/E | 9000 | 3300 | 3000K | 81 | 3 11/16 | Universal | 12 |
| 39 | SE Tubular | G12 | S4288 | CDM35/T6/830 | Clear | M130/E | 12000 | 3400 | 3000K | 81 | 3 5/16 | Universal | 12 |
| 70 | SE Tubular | G8.5 | S4287 | CDM70/TC/830 | Clear | M139/E | 6000 | 6400 | 3000K | 83 | 3 11/16 | Universal | 12 |
| 70 | SE Tubular | G12 | S4289 | CDM70/T6/830 | Clear | M139/E | 12000 | 6600 | 3000K | 81 | 3 5/16 | Universal | 12 |
| 70 | SE Tubular | G12 | S4264 | CDM70/T6/942 | Clear | M139/E | 12000 | 6600 | 4200K | 92 | 3 5/16 | Universal | 12 |
| 70 | DE Tubular | RX7 | S4292 | CDM70/TD/830 | Clear | M139/M85/E | 15000 | 6500 | 3000K | 82 | 4 11/16 | HOR±45° | 12 |
| 70 | DE Tubular | RX7 | S4265 | CDM70/TD/942 | Clear | M139/M85/E | 15000 | 6000 | 4200K | 92 | 4 11/16 | HOR±45° | 12 |
| 150 | SE Tubular | G12 | S4290 | CDM150/T6/830 | Clear | M142/E | 12000 | 14000 | 3000K | 85 | 4 11/16 | Universal | 12 |
| 150 | SE Tubular | G12 | S4266 | CDM150/T6/942 | Clear | M142/E | 9000 | 12700 | 4200K | 96 | 4 11/16 | Universal | 12 |
| 150 | DE Tubular | RX7 | S4293 | CDM150/TD/830 | Clear | M142/M102/M81/E | 15000 | 13250 | 3000K | 88 | 5 7/16 | HOR±45° | 12 |
| 150 | DE Tubular | RX7 | S4267 | CDM150/TD/942 | Clear | M142/M102/M81/E | 15000 | 14200 | 4200K | 96 | 5 7/16 | HOR±45° | 12 |

Metal Halide

- Pulse Start
- Enclosed Rated
- Universal – Varied Burning Position

Not Shown Actual Size



| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Finish | ANSI | Avg. Life Hours | Initial Lumens | Color Temp | CRI | M.O.L. | Operating Position | Case Qty. |
|-------|-----------|------|-----------------|-----------------|--------|--------|-----------------|----------------|------------|-----|--------|--------------------|-----------|
| 70 | ED28 | Mog. | S4230 | MH70/U/ED28/PS | Clear | M98/E | 15000 | 5600 | 4000 | 65 | 8 5/8" | Univ. | 12 |
| 100 | ED28 | Mog. | S4231 | MH100/U/ED28/PS | Clear | M90/E | 15000 | 9000 | 4000 | 65 | 8 5/8" | Univ. | 12 |
| 125 | ED17 | Med. | S4232 | MH125/HBU/PS | Clear | M150/E | 15000 | 1200 | 4000 | 65 | 5 5/8" | BU±90° | 12 |
| 150 | ED28 | Mog. | S4233 | MH150/U/ED28/PS | Clear | M102/E | 15000 | 14000 | 4000 | 65 | 8 5/8" | Univ. | 12 |

- Energy Saver
- Standard Start
- Enclosed Rated
- Specified Burning Position
- Medium Base



| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Finish | ANSI | Avg. Life Hours | Initial Lumens | Color Temp | CRI | M.O.L. | Operating Position | Case Qty. |
|-------|-----------|----------|-----------------|----------------|--------|-------|-----------------|----------------|------------|-----|---------|--------------------|-----------|
| 360 | ED37 | E39/Mog. | S4476 | MS360W/BU/EM | Clear | M165E | 20000 | 36000 | 4000 | 65 | 11 1/2" | BU±15° | 6 |
| 360 | ED37 | E39/Mog. | S4477 | MS360W/C/BU/EM | Coated | M165E | 20000 | 34200 | 3700 | 70 | 11 1/2" | BU±15° | 6 |

Metal Halide



Clear **ED37** Coated

- Open Rated
- Energy Saver
- Standard Start
- Specified Burning Position
- Mogul Base

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Finish | ANSI | Avg. Life Hours | Initial Lumens | Color Temp | CRI | M.O.L. | Operating Position | Case |
|-------|-----------|-----------|-----------------|-----------------|--------|-------|-----------------|----------------|------------|-----|--------|--------------------|------|
| 360 | ED37 | EX39/Mog. | S4478 | MPI360W/BU/EM | Clear | M165O | 20000 | 35000 | 4000 | 65 | 11½ | BU±15° | 6 |
| 360 | ED37 | EX39/Mog. | S4479 | MPI360W/C/BU/EM | Coated | M165O | 20000 | 34000 | 3700 | 70 | 11½ | BU±15° | 6 |



Clear **ED37** Coated **ED28**

- "White Lux" HPS Replacement
- Standard Start
- Enclosed Rated
- Specified Burning Position
- Mogul Base

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Finish | ANSI | Avg. Rated Hours | Initial Lumens | Color Temp | CRI | M.O.L. | Operating Position | Case |
|-------|-----------|------|-----------------|----------------|--------|-------|------------------|----------------|------------|-----|--------|--------------------|------|
| 250 | ED28 | Mog. | S4268 | MS250W/BU/LU | Clear | S50/E | 10000 | 18500 | 4000 | 65 | 8 5/16 | BU±15° | 12 |
| 400 | ED37 | Mog. | S4269 | MS400W/BU/LU | Clear | S51/E | 20000 | 38000 | 4000 | 65 | 11½ | BU±15° | 6 |
| 400 | ED37 | Mog. | S4270 | MS400W/C/BU/LU | Coated | S51/E | 20000 | 36000 | 3700 | 70 | 11½ | BU±15° | 6 |

Mercury Vapor

Coated Finish

Mogul Base

Not Shown Actual Size



ED23^{1/2}

S1935 100W H38JA-100/DX
Packing: 12/Master



ED28

S1934 175W H39KC-175/DX
S1937 250W H37KC-250/DX
Packing: 12/Master



ED37

S1938 400W H33GL-400/DX
Packing: 6/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Hours | Initial Lumens | M.O.L. | Case |
|-------|-----------|-------|-----------------|-------------|--------|------------------|----------------|---------|------|
| 100 | ED23 1/2 | Mogul | S1935 | H38JA-100DX | Coated | 10000 | 4000 | 7 1/2" | 12 |
| 175 | ED28 | Mogul | S1934 | H39KC-175DX | Coated | 10000 | 7800 | 8 5/16" | 12 |
| 250 | ED28 | Mogul | S1937 | H37KC-250DX | Coated | 10000 | 11200 | 8 5/16" | 12 |
| 400 | ED37 | Mogul | S1938 | H33GL-400DX | Coated | 10000 | 22600 | 11 1/2" | 12 |

Mercury Vapor Clear & Coated



Not Shown Actual Size



ED28

**Clear
Mogul Base**

S1936 175W H39KB-175
Packing: 12/Master



ED17

**Coated
Medium Base**

S4474 50W H45/46DL-40/50DX
S4475 75W H43AV-75/DX
Packing: 12/Master



A23

**Coated
Medium Base**

S1933 100W H38MP-100/DX
Packing: 12/Master

HID lamps

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Hours | Initial Lumens | M.O.L. | Case |
|-------|-----------|--------|-----------------|------------------|--------|------------------|----------------|--------|------|
| 50 | ED17 | Medium | S4474 | H45/46DL-40/50DX | Coated | 6000 | 1580 | 5 1/8" | 12 |
| 75 | ED17 | Medium | S4475 | H43AV-75/DX | Coated | 6000 | 2700 | 5 1/8" | 12 |
| 100 | A23 | Medium | S1933 | H38MP-100DX | Coated | 6000 | 4000 | 5 1/8" | 12 |
| 175 | ED28 | Mogul | S1936 | H39KB-175 | Clear | 10000 | 7800 | 8 3/8" | 12 |

High Pressure Sodium



Clear & Coated Medium Base

Not Shown Actual Size



E17



E17

Four color retail display carton

- S5120** 35W LU35/D/MED
- S5121** 50W LU50/D/MED
- S3123** 70W LU70/D/MED
- S5125** 100W LU100/D/MED
- S5127** 150W LU150/55/D/MED

Packing: 20/Master

- S3130** 35W LU35/MED
- S3131** 50W LU50/MED
- S3127** 70W LU70/MED
- S3128** 100W LU100/MED
- S3129** 150W LU150/55/MED

Packing: 12/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Hours | Initial Lumens | M.O.L. | Case |
|-------|-----------|--------|-----------------|----------------|--------|------------------|----------------|----------|------|
| 35 | E17 | Medium | S3130 | LU35/MED | Clear | 16000 | 2250 | 5 7/16" | 12 |
| 35 | E17 | Medium | S5120 | LU35/D/MED | Coated | 16000 | 2100 | 5 7/16" | 20 |
| 50 | E17 | Medium | S3131 | LU50/MED | Clear | 24000 | 4000 | 5 7/16" | 12 |
| 50 | E17 | Medium | S5121 | LU50/D/MED | Coated | 24000 | 3700 | 5 7/16" | 20 |
| 70 | E17 | Medium | S3127 | LU70/MED | Clear | 24000 | 6300 | 5 7/16" | 12 |
| 70 | E17 | Medium | S5123 | LU70/D/MED | Coated | 24000 | 5800 | 5 7/16" | 20 |
| 100 | E17 | Medium | S3128 | LU100/MED | Clear | 24000 | 9500 | 5 7/16" | 12 |
| 100 | E17 | Medium | S5125 | LU100/D/MED | Coated | 24000 | 8800 | 5 7/16" | 20 |
| 150 | E17 | Medium | S3129 | LU150/55/MED | Clear | 24000 | 15800 | 5 11/16" | 12 |
| 150 | E17 | Medium | S5127 | LU150/55/D/MED | Coated | 24000 | 14500 | 5 11/16" | 20 |



High Pressure Sodium

24,000 Hours

Clear & Coated

Mogul Base

Not Shown Actual Size



ET23 1/2



ET23 1/2

- S1929** 50W LU50
 - S1930** 70W LU70
 - S1931** 100W LU100
 - S1932** 150W LU150/55
- Packing: 12/Master

- S5122** 50W LU50/D
 - S5160** 70W LU70/D
 - S5126** 100W LU100/D
 - S5128** 150W LU150/55/D
- Packing: 20/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Hours | Initial Lumens | M.O.L. | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|------------|--------|------------------|----------------|--------|-----------------------|
| 50 | ET23 1/2 | Mogul | S1929 | LU50 | Clear | 24000 | 4000 | 7 3/4" | 12 |
| 50 | ET23 1/2 | Mogul | S5122 | LU50/D | Coated | 24000 | 3700 | 7 3/4" | 20 |
| 70 | ET23 1/2 | Mogul | S1930 | LU70 | Clear | 24000 | 6300 | 7 3/4" | 12 |
| 70 | ET23 1/2 | Mogul | S5160 | LU70/D | Coated | 24000 | 5500 | 7 3/4" | 20 |
| 100 | ET23 1/2 | Mogul | S1931 | LU100 | Clear | 24000 | 9500 | 7 3/4" | 12 |
| 100 | ET23 1/2 | Mogul | S5126 | LU100/D | Coated | 24000 | 8800 | 7 3/4" | 20 |
| 150 | ET23 1/2 | Mogul | S1932 | LU150/55 | Clear | 24000 | 16000 | 7 3/4" | 12 |
| 150 | ET23 1/2 | Mogul | S5128 | LU150/55/D | Coated | 24000 | 14000 | 7 3/4" | 20 |

H I D l a m p s

High Pressure Sodium



Clear Mogul Base

24,000 Hours

Not Shown Actual Size



ET18

S5129 200W LU200/ECO
 S1940 250W LU250
 S5131 310W LU310/ECO
 S1941 400W LU400



E25

S5124 1000W LU1000

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Hours | Initial Lumens | M.O.L. | Case |
|-------|-----------|-------|-----------------|-----------|--------|------------------|----------------|----------|------|
| 200 | ET18 | Mogul | S5129 | LU200/ECO | Clear | 24000 | 22000 | 9 5/8" | 20 |
| 250 | ET18 | Mogul | S1940 | LU250 | Clear | 24000 | 28000 | 9 5/8" | 12 |
| 310 | ET18 | Mogul | S5131 | LU310/ECO | Clear | 24000 | 37000 | 9 5/8" | 20 |
| 400 | ET18 | Mogul | S1941 | LU400 | Clear | 24000 | 51000 | 9 5/8" | 12 |
| 1000 | E25 | Mogul | S5124 | LU1000 | Clear | 24000 | 130000 | 15 1/16" | 6 |

High Pressure Sodium

Clear & Coated Mogul Base

24,000 Hours



BT37

BT37

BT28

S5133 750W LU750
Packing: 6/Master

S5132 400W LU400/D
Packing: 10/Master

S5130 250W LU250/D
Packing: 10/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Hours | Initial Lumens | M.O.L. | Case |
|-------|-----------|-------|-----------------|-----------|--------|------------------|----------------|----------|------|
| 250 | BT28 | Mogul | S5130 | LU250/D | Coated | 24000 | 26000 | 8 31/32" | 10 |
| 400 | BT37 | Mogul | S5132 | LU400/D | Coated | 24000 | 47500 | 11 1/2" | 10 |
| 750 | BT37 | Mogul | S5133 | LU750/ECO | Clear | 24000 | 105000 | 11 1/2" | 6 |

Low Pressure

Sodium Sox Lamps

16,000 Hours

T17

S4870 18W SOX18W
S4871 35W SOX35W
S4872 55W SOX55W

Packing: 12/Master

T21

S4873 90W SOX90W
S4874 135W SOX135W

Packing: 12/Master

S4875 180W SOX180W

Packing: 9/Master

Not Shown
Actual Size



| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Avg. Rated Hours | Initial Lumens | Burning Position | M.O.L. | Case |
|-------|-----------|-------|-----------------|-----------|--------|------------------|----------------|------------------|--------|------|
| 18 | T17 | BY22d | S4870 | SOX18W | Clear | 16000 | 1800 | BU±110° | 8 ½" | 12 |
| 35 | T17 | BY22d | S4871 | SOX35W | Clear | 16000 | 4500 | BU±110° | 12 ¾" | 12 |
| 55 | T17 | BY22d | S4872 | SOX55W | Clear | 16000 | 7300 | BU±110° | 16 ¾" | 12 |
| 90 | T21 | BY22d | S4873 | SOX90W | Clear | 16000 | 13500 | H±20° | 20 ¾" | 12 |
| 135 | T21 | BY22d | S4874 | SOX135W | Clear | 16000 | 22000 | H±20° | 30 ½" | 12 |
| 180 | T21 | BY22d | S4875 | SOX180W | Clear | 16000 | 30000 | H±20° | 44 ½" | 9 |

Sealed Beam Lamps

PAR36

sealed beam lamps



PAR36 Screw Terminal

2 Piece Construction

Not Shown Actual Size

| Watts | Bulb Type | Base | Salco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP | Filament | M.O.L. | Mst. Ctn./ Pack | Inner Type | Pack |
|---------------------|-----------|-------------|-----------------|---------------------------------|-----------|-------|------------------|-------|----------|--------|-----------------|------------|------|
| HALOGEN | | | | | | | | | | | | | |
| 36 | PAR36 | Screw Term. | S4807 | 36PAR36/CAP/VNSP | Spot 5° | 12V | 4000 | 17000 | CC-8 | 2 3/4" | Box | 12 | |
| 36 | PAR36 | Screw Term. | S4808 | 36PAR36/CAP/NSP | Spot 13° | 12V | 4000 | 3500 | CC-8 | 2 3/4" | Box | 12 | |
| 36 | PAR36 | Screw Term. | S4809 | 36PAR36/CAP/FL | Flood 32° | 12V | 4000 | 1000 | CC-8 | 2 3/4" | Box | 12 | |
| 50 | PAR36 | Screw Term. | S4806 | 50PAR36/CAP/NSP | Spot 6° | 12V | 4000 | 25000 | CC-8 | 2 3/4" | Box | 12 | |
| INCANDESCENT | | | | | | | | | | | | | |
| 50 | PAR36 | Screw Term. | S4804 | 50PAR36/WFL | Flood 30° | 12V | 2000 | 11500 | CC-6 | 2 3/4" | Box | 12 | |
| 50 | PAR36 | Screw Term. | S4805 | 50PAR36/SP | Spot 15° | 12V | 2000 | 11500 | CC-6 | 2 3/4" | Box | 12 | |
| 300 | PAR56 | Screw Term. | S4810 | 300PAR56/MFL | Flood 22° | 120V | 2000 | 24000 | CC-13 | 5" | Box | 8 | |
| 300 | PAR56 | Screw Term. | S4811 | 300PAR56/WFL | Flood 37° | 120V | 2000 | 11000 | CC-13 | 5" | Box | 8 | |
| 18 | PAR36 | Screw Term. | S4300 | 4014/Emergency Bldg. Lighting | | 6.4V | 200 | | | 2 3/4" | Box | 12 | |
| 12 | PAR36 | Screw Term. | S4301 | 4042/Emergency Bldg. Lighting | | 6.4V | 150 | | | 2 3/4" | Box | 12 | |
| 12 | PAR36 | Screw Term. | S4302 | 4044-1/Emergency Bldg. Lighting | | 12V | 150 | | | 2 3/4" | Box | 12 | |
| 30 | PAR36 | Screw Term. | S4303 | 4405/Spot Light | | 12.8V | 100 | | | 2 3/4" | Box | 12 | |
| 35 | PAR36 | Screw Term. | S4304 | 4406/Tractor, Flood | | 12.8V | 300 | | | 2 3/4" | Box | 12 | |
| 35 | PAR36 | Screw Term. | S4305 | 4411/Tractor | | 12.8V | 300 | | | 2 3/4" | Box | 12 | |
| 18 | PAR36 | Screw Term. | S4306 | 4414/Warning Signal, Emergency | | 12.8V | 300 | | | 2 3/4" | Box | 12 | |
| 35 | PAR36 | Screw Term. | S4307 | 4415/Fog | | 12.8V | 300 | | | 2 3/4" | Box | 12 | |
| 30 | PAR36 | Screw Term. | S4316 | 4416/Spotlamp, Signal | | 12.8V | 100 | | | 2 3/4" | Box | 12 | |
| 25 | PAR36 | Screw Term. | S4317 | 4446/Emergency Bldg. Lighting | | 12.8V | 300 | | | 2 3/4" | Box | 12 | |

Continued on next page

Sealed Beam Lamps

PAR36 & PAR46



PAR46 Screw Terminal

2 Piece Construction

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn./ Inner Pack |
|--------------|-----------|-------------|-----------------|---|------|-------|------------------|--------|----------|--------|------------|-----------------------|
| 50 | PAR36 | Screw Term. | S4318 | 4502/Auto Headlamp, Military | | 28V | 400 | | | 2 3/4" | Box | 12 |
| 50 | PAR36 | Screw Term. | S4319 | 4505/Aircraft, Navigation | | 28V | 400 | | | 2 3/4" | Box | 12 |
| 100 | PAR36 | Screw Term. | S4320 | 4509/Aircraft, Landing, Spotlamp | | 13V | 25 | | | 2 3/4" | Box | 12 |
| 25 | PAR36 | Screw Term. | S4321 | 4510/Tractor, Flood, Emergency Bldg. | | 6.4V | 300 | | | 2 3/4" | Box | 12 |
| 30 | PAR36 | Screw Term. | S4322 | 4515/Spotlamp | | 6.4V | 100 | | | 2 3/4" | Box | 12 |
| 30 | PAR36 | Screw Term. | S4323 | 4516/Spotlamp | | 6.2V | 100 | | | 2 3/4" | Box | 12 |
| 0.50A | PAR36 | Multi Term. | S4324 | 4546-1/Hand Lantern | | 4.75V | 100 | | | 2 3/4" | Box | 12 |
| 8 | PAR36 | Screw Term. | S4325 | H7550/Hand Lantern, Halogen | | 6V | 50 | | | 2 3/4" | Box | 12 |
| 8 | PAR36 | Screw Term. | S4326 | H7551/Emergency Bldg. Lighting, Halogen | | 6V | 50 | | | 2 3/4" | Box | 12 |
| 10 | PAR36 | Screw Term. | S4327 | H7552/Emergency Bldg. Lighting, Halogen | | 6V | 50 | | | 2 3/4" | Box | 12 |
| 12 | PAR36 | Screw Term. | S4328 | H7553/Emergency Bldg. Lighting, Halogen | | 6V | 50 | | | 2 3/4" | Box | 12 |
| 20 | PAR36 | Screw Term. | S4329 | H7554/Emergency Bldg., Halogen | | 6V | 50 | | | 2 3/4" | Box | 12 |
| 8 | PAR36 | Screw Term. | S4330 | H7555/Emergency Bldg. Lighting, Halogen | | 12V | 50 | | | 2 3/4" | Box | 12 |
| 6 | PAR36 | Screw Term. | S4331 | H7556/Emergency Bldg. Halogen | | 6V | 50 | | | 2 3/4" | Box | 12 |
| 12 | PAR36 | Screw Term. | S4332 | H7557/Emergency Bldg. Lighting, Halogen | | 12V | 50 | | | 2 3/4" | Box | 12 |
| 8 | PAR36 | Screw Term. | S4333 | 7613/Emergency Bldg. Lighting | | 6V | 50 | | | 2 3/4" | Box | 12 |
| 7.2 | PAR36 | Screw Term. | S4334 | 7672-1/Emergency Bldg. Lighting | | 6V | 50 | | | 2 3/4" | Box | 12 |
| PAR46 | | | | | | | | | | | | |
| 30 | PAR46 | Screw Term. | S4335 | 4435/Spotlamp | | 12.8V | 100 | | | 2 3/4" | Box | 12 |
| 30 | PAR46 | Screw Term. | S4336 | 4535/Spotlamp | | 6.4V | 100 | | | 2 3/4" | Box | 12 |

Sealed Beam Lamps

PAR56 & PAR64



PAR56
Mogul End Prong

2 Piece Construction
120 Volt

S4668 500 Watt Narrow Spot

S4669 500 Watt Med. Flood

S4670 500 Watt Wide Flood

Packing: Individually Boxed
12/Master

PAR64
Mogul End Prong

2 Piece Construction
120 Volt

S4671 1000 Watt Narrow Spot

S4672 1000 Watt Med. Flood

S4673 1000 Watt Wide Flood

Packing: Individually Boxed
12/Master

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Beam | Volts | Avg. Rated Hours | CBCP* | Lumens | Filament | M.O.L. | Pack. Type | Mst. Ctn. |
|-------|-----------|-----------------|-----------------|----------------|--------------------|-------|------------------|-------|--------|----------|--------|------------|-----------|
| 500 | PAR56 | Mogul End Prong | S4668 | 500PAR56Q/NSP | Narrow Spot 8X15° | 120V | 4000 | 78500 | 8800 | C,CC-6 | 5" | Box | 12 |
| 500 | PAR56 | Mogul End Prong | S4669 | 500PAR56Q/MFL | Med.Flood 11X30° | 120V | 4000 | 40000 | 8800 | C,CC-6 | 5" | Box | 12 |
| 500 | PAR56 | Mogul End Prong | S4670 | 500PAR56Q/WFL | Wide Flood 20X45° | 120V | 4000 | 19500 | 8800 | C,CC-6 | 5" | Box | 12 |
| 1000 | PAR64 | Mogul End Prong | S4671 | 1000PAR64Q/NSP | Narrow Spot 18X20° | 120V | 4000 | 40000 | 19400 | C,CC-6 | 6" | Box | 6 |
| 1000 | PAR64 | Mogul End Prong | S4672 | 1000PAR64Q/MFL | Med.Flood 10X30° | 120V | 4000 | 82000 | 19400 | C,CC-6 | 6" | Box | 6 |
| 1000 | PAR64 | Mogul End Prong | S4673 | 1000PAR64Q/WFL | Wide Flood 20X60° | 120V | 4000 | 23000 | 19400 | C,CC-6 | 6" | Box | 6 |

Miniature *Incandescent* Lamps



Sub Miniature
Wedge Base

Midget Flange
Base

T-1³/₄

Indicator • Aircraft • Toy • Auto • P.C. Board

S6900 #73 Sub Miniature Wedge Base

S6901 #85 Sub Miniature Wedge Base

S6902 #86 Sub Miniature Wedge Base

S6903 #327 Midget Flange Base

E387 #387 Midget Flange Base

Packing: 10 Bulbs/Sleeve



T-2

Switch Board • Pilot
Indicator

**Miniature
Slide Base**

S6904 #24PSB5

E28PSB5 #28PSB5

S6838 #48PSB5

E120PSB5 #120PSB5

S6841 #155PSB5

Packing: 10 Bulbs/Sleeve



T-2¹/₂

Switch Board • Pilot
Indicator

**Miniature
Bayonet Base**

E24MB #24MB

E28MB #28MB

S6844 #48MB

S6905 #120MB

E130MB #130MB

S6849 #155MB

Packing: 10 Bulbs/Sleeve

Not Shown Actual Size

| Bulb Type | Base | Satco Order No. | Lamp Code | Amps | Volts | Avg. Rated Hours | Filament | M.O.L. | Mst. Ctn./ Inner Pack |
|---------------------------------|---------------|--------------------|-----------|------|-------|---------------------|----------|--------|--------------------------|
| T-1 ³ / ₄ | Mini Wedge | S6900 | 73 | .08 | 14V | 15000 | C-2F | .80" | 10 |
| T-1 ³ / ₄ | Mini Wedge | S6901 | 85 | .04 | 18V | 7000 | C-2F | .80" | 10 |
| T-1 ³ / ₄ | Mini Wedge | S6902 | 86 | .15 | 6.3V | 20000 | C-2F | .80" | 10 |
| T-1 ³ / ₄ | Midget Flange | S6903 | 327 | .04 | 28V | 4000 | C-2F | .80" | 10 |
| T-1 ³ / ₄ | Midget Flange | E387 | 387 | .04 | 28V | 10000 | C-2F | .625" | 10 |
| T-2 | Slide | S6904 | 24PSB5 | .073 | 24V | 10000 | C-2F | 1.12" | 10 |
| T-2 | Slide | E28PSB5 | 28PSB5 | .04 | 28V | 5000 | C-2F | 1.10" | 10 |
| T-2 | Slide | S6838 | 48PSB5 | .05 | 48V | 10000 | C-7A | 1.10" | 10 |
| T-2 | Slide | E120PSB5 | 120PSB5 | .025 | 120V | 10000 | CC-7A | 1.10" | 10 |
| T-2 | Slide | S6841 | 155PSB5 | .025 | 155V | 10000 | CC-7A | 1.12" | 10 |
| T-2 ¹ / ₂ | Mini Bayonet | E24MB | 24MB | .07 | 24V | 10000 | C-2F | 1.19" | 10 |
| T-2 ¹ / ₂ | Mini Bayonet | E28MB | 28MB | .04 | 28V | 5000 | C-2F | 1.19" | 10 |
| T-2 ¹ / ₂ | Mini Bayonet | S6844 | 48MB | .053 | 48V | 5000 | C-7A | 1.19" | 10 |
| T-2 ¹ / ₂ | Mini Bayonet | E120MB | 120MB | .025 | 120V | 10000 | CC-7A | 1.19" | 10 |
| T-2 ¹ / ₂ | Mini Bayonet | E130MB | 130MB | .03 | 130V | 10000 | CC-7A | 1.19" | 10 |
| T-2 ¹ / ₂ | Mini Bayonet | S6849 | 155MB | .025 | 155V | 10000 | CC-7A | 1.19" | 10 |

Miniature

Incandescent Lamps



Wedge Base

Min. Bay. Base

Mini Screw Base

T-3 1/4

Radio • Indicator • Auto

- | | |
|------------------------------------|-----------------------------------|
| S6908 #40 Min. Screw Base | S6918 #755 Min. Bay. Base |
| S6909 #41 Min. Screw Base | S6919 #756 Min. Bay. Base |
| S6911 #46 Min. Screw Base | S6920 #757 Min. Bay. Base |
| S6913 #48 Min. Screw Base | S6856 #967 Min. Bay. Base |
| E1487 #1487 Min. Screw Base | E1810 #1810 Min. Bay. Base |
| E147 #147 Wedge Base | E1813 #1813 Min. Bay. Base |
| S6914 #161 Wedge Base | E1815 #1815 Min. Bay. Base |
| S6915 #168 Wedge Base | E1818 #1818 Min. Bay. Base |
| E193 #193 Wedge Base | E1819 #1819 Min. Bay. Base |
| S6916 #194 Wedge Base | E1820 #1820 Min. Bay. Base |
| E400 #400 Wedge Base | E1829 #1829 Min. Bay. Base |
| E464 #464 Wedge Base | E1835 #1835 Min. Bay. Base |
| S6910 #44 Min. Bay. Base | E1864 #1864 Min. Bay. Base |
| S6912 #47 Min. Bay. Base | |
| S6917 #313 Min. Bay. Base | |

Packing: 10 Bulbs/Sleeve



T-3

Auto • Indicator

D.E. Caps

S6906 #211-2

Packing:
10 Bulbs/Sleeve



TL-3

Flashlight

Mini Screw Base

S6907 #222

Packing:
10 Bulbs/Sleeve

Not Shown Actual Size

| Bulb Type | Base | Satco Order No. | Lamp Code | Amps | Volts | Avg. Rated Hours | Filament | M.O.L. | Mst. Ctn./ Inner Pack |
|-----------|--------------|-----------------|-----------|-------|-------|------------------|----------|--------|-----------------------|
| T-3 | D.E. Caps | S6906 | 211-2 | 0.97 | 12.8V | 1000 | C-8 | 1.72" | 10 |
| TL-3 | Mini Screw | S6907 | 222 | 0.25 | 2.25V | 5 | C-2R | .93" | 10 |
| T-3 1/4 | Mini Screw | S6908 | 40 | 0.15 | 6.3V | 3000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Screw | S6909 | 41 | 0.5 | 2.5V | 3000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Screw | E1487 | 1487 | 0.2 | 14V | 500 | C-2F | 1.19" | 10 |
| T-3 1/4 | Mini Screw | S6911 | 46 | 0.25 | 6.3V | 3000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Screw | S6913 | 48 | 0.06 | 2.0V | 1000 | C-6 | 1.19" | 10 |
| T-3 1/4 | Wedge | E147 | 147 | 0.043 | 7V | 1500 | C-2R | 1.06" | 10 |
| T-3 1/4 | Wedge | S6914 | 161 | 0.08 | 14V | 4000 | C-2F | 1.06" | 10 |
| T-3 1/4 | Wedge | E193 | 193 | 0.033 | 14V | 7500 | C-2F | 1.06" | 10 |
| T-3 1/4 | Wedge | S6915 | 168 | 0.35 | 14V | 1500 | C-2F | 1.06" | 10 |
| T-3 1/4 | Wedge | S6916 | 194 | 0.27 | 14V | 2500 | C-2F | 1.06" | 10 |
| T-3 1/4 | Wedge | E400 | 400 | 0.1 | 28V | 1000 | C-2F | 1.06" | 10 |
| T-3 1/4 | Wedge | E464 | 464 | 0.17 | 28V | 1500 | C-2F | 1.06" | 10 |
| T-3 1/4 | Mini Bayonet | S6910 | 44 | 0.25 | 6.3V | 3000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | S6912 | 47 | 0.25 | 6.3V | 3000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | S6917 | 313 | 0.2 | 28V | 500 | C-2F | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | S6918 | 755 | 0.15 | 6.3V | 20000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | S6919 | 756 | 0.08 | 14V | 15000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | S6920 | 757 | 0.08 | 14V | 15000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | S6856 | 967 | 0.02 | 130V | 7000 | CC-7A | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1810 | 1810 | 0.4 | 6.3V | 3000 | C-2R | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1813 | 1813 | 0.1 | 14.4V | 1000 | C-2V | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1815 | 1815 | 0.2 | 14V | 3000 | C-2F | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1818 | 1818 | 0.17 | 24V | 250 | C-2F | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1819 | 1819 | 0.04 | 28V | 2500 | C-2F | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1820 | 1820 | 0.1 | 28V | 1000 | C-2F | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1829 | 1829 | 0.07 | 28V | 1000 | C-2F | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1835 | 1835 | 0.05 | 55V | 5000 | C-2F | 1.19" | 10 |
| T-3 1/4 | Mini Bayonet | E1864 | 1864 | 0.17 | 28V | 1500 | C-2F | 1.19" | 10 |

miniature lamps

Miniature

Incandescent Lamps



B-3 1/2

Flashlight • Lantern
S.C. Min. Flange Base

- S6921 #PR2**
- S6922 #PR3**
- S6923 #PR4**
- S6924 #PR6**
- S6925 #PR7**
- S6926 #PR12**
- S6927 #PR13**
- S6928 #PR30**

Packing:
 10 Bulbs/Sleeve



Mini 2 Pin Mini Bay Base Mini Screw Base

G-3 1/2

Flashlight • Bicycle • Indicator • Radio

- S6929 #10 Min. 2 Pin Base**
- S6930 #12 Min. 2 Pin Base**
- S6931 #14 Min. Screw Base**
- S6932 #19 Min. 2 Pin Base**
- S6933 #51 Min. Bay Base**
- S6934 #53 Min. Bay Base**

Packing:
 10 Bulbs/Sleeve



Mini Bay Base Mini Screw Base

G-4 1/4

Toy • Lantern • Flashlight • Indicator

- S6935 #57 Min. Bay Base**
- S6936 #425 Min. Screw Base**
- S6937 #502 Min. Screw Base**

Packing:
 10 Bulbs/Sleeve

Not Shown Actual Size

| Bulb Type | Base | Satco Order No. | Lamp Code | Amps | Volts | Avg. Rated Hours | Filament | M.O.L. | Mst. Ctn./ Inner Pack |
|-----------|--------------|-----------------|-----------|------|-------|------------------|----------|--------|-----------------------|
| B-3 1/2 | Flange | S6921 | PR2 | .50 | 2.38V | 15 | C-2R | 1.25" | 10 |
| B-3 1/2 | Flange | S6922 | PR3 | .50 | 3.57V | 15 | C-2R | 1.25" | 10 |
| B-3 1/2 | Flange | S6923 | PR4 | .27 | 2.33V | 10 | C-2R | 1.25" | 10 |
| B-3 1/2 | Flange | S6924 | PR6 | .30 | 2.47V | 30 | C-2R | 1.25" | 10 |
| B-3 1/2 | Flange | S6925 | PR7 | .30 | 3.70V | 30 | C-2R | 1.25" | 10 |
| B-3 1/2 | Flange | S6926 | PR12 | .50 | 5.75V | 15 | C-2R | 1.25" | 10 |
| B-3 1/2 | Flange | S6927 | PR13 | .50 | 4.75V | 15 | C-2R | 1.25" | 10 |
| B-3 1/2 | Flange | S6928 | PR30 | .86 | 3.75V | 40 | C-2R | 1.25" | 10 |
| G-3 1/2 | 2 Pin | S6929 | 10 | .300 | 2.47V | 3000 | C-6 | .94" | 10 |
| G-3 1/2 | 2 Pin | S6930 | 12 | .150 | 6.30V | 5000 | C-6 | .94" | 10 |
| G-3 1/2 | Mini Screw | S6931 | 14 | .30 | 2.47V | 15 | C-2R | .94" | 10 |
| G-3 1/2 | 2 Pin | S6932 | 19 | .10 | 14.4V | 1000 | C-6 | .94" | 10 |
| G-3 1/2 | Mini Bayonet | S6933 | 51 | .220 | 7.5V | 1000 | C-2R | .94" | 10 |
| G-4 1/2 | Mini Bayonet | S6934 | 53 | .120 | 14.4V | 1000 | C-2V | .94" | 10 |
| G-4 1/2 | Mini Bayonet | S6935 | 57 | .24 | 14.4V | 500 | C-2V | 1.06" | 10 |
| G-4 1/2 | Mini Screw | S6936 | 425 | .50 | 5.0V | 15 | C-2R | 1.06" | 10 |
| G-4 1/2 | Mini Screw | S6937 | 502 | .15 | 5.1V | 100 | C-2R | 1.06" | 10 |

Miniature *Incandescent* Lamps



S.C. Bayonet Base

D.C. Bayonet Base

G-6

Auto • Indicator • Aircraft

- S6946** #63 S.C. Bayonet Base
- S6947** #67 S.C. Bayonet Base
- S6948** #89 S.C. Bayonet Base
- S6949** #90 D.C. Bayonet Base
- S6950** #97 D.C. Bayonet Base

Packing: 10 Bulbs/Sleeve



S.C. Bayonet Base

D.C. Bayonet Base

B-6

Aircraft • Auto • Indicator

- S6951** #1003 S.C. Bayonet Base
- S6952** #1004 D.C. Bayonet Base

Packing: 10 Bulbs/Sleeve



T-5

Auto • Indicator • Special • Service

Mini Wedge Base

- S6938** #901
- S6939** #904
- S6940** #906
- S6941** #908
- S6942** #909
- S6943** #912
- S6944** #918
- S6945** #921
- E922** #922
- E939** #939

Packing: 10 Bulbs/Sleeve

Not Shown Actual Size

| Bulb Type | Base | Satco Order No. | Lamp Code | Amps | Volts | Avg. Rated Hours | Filament | M.O.L. | Mst.Ctn./ Inner Pack |
|-----------|--------------|-----------------|-----------|------|-------|------------------|----------|--------|----------------------|
| T-5 | Mini Wedge | S6938 | 901 | .31 | 12.8V | 500 | C-2R | 1.49" | 10 |
| T-5 | Mini Wedge | S6939 | 904 | .69 | 13.5V | 5000 | C-2F | 1.49" | 10 |
| T-5 | Mini Wedge | S6940 | 906 | .69 | 13.0V | 1000 | C-2F | 1.49" | 10 |
| T-5 | Mini Wedge | S6941 | 908 | 1.5 | 6.0V | 50 | C-2R | 1.49" | 10 |
| T-5 | Mini Wedge | S6942 | 909 | .62 | 6.0V | 50 | C-2R | 1.49" | 10 |
| T-5 | Mini Wedge | S6943 | 912 | 1.0 | 12.8V | 1000 | C-2R | 1.49" | 10 |
| T-5 | Mini Wedge | S6944 | 918 | .56 | 12.8V | 500 | C-2R | 1.49" | 10 |
| T-5 | Mini Wedge | S6945 | 921 | 1.4 | 12.8V | 1000 | C-2R | 1.49" | 10 |
| T-5 | Mini Wedge | E922 | 922 | 0.98 | 12.8V | 200 | C-2R | 1.49" | 10 |
| T-5 | Mini Wedge | E939 | 939 | 0.9 | 6V | 200 | C-6 | 1.49" | 10 |
| G-6 | S.C. Bayonet | S6946 | 63 | .63 | 7.0V | 1000 | C-6 | 1.44" | 10 |
| G-6 | S.C. Bayonet | S6947 | 67 | .59 | 13.5V | 5000 | C-6 | 1.44" | 10 |
| G-6 | S.C. Bayonet | S6948 | 89 | .58 | 13.0V | 750 | C-6 | 1.44" | 10 |
| G-6 | D.C. Bayonet | S6949 | 90 | .58 | 13.0V | 750 | C-6 | 1.44" | 10 |
| G-6 | D.C. Bayonet | S6950 | 97 | .59 | 13.5V | 5000 | C-6 | 1.44" | 10 |
| B-6 | S.C. Bayonet | S6951 | 1003 | .94 | 12.8V | 200 | C-6 | 1.75" | 10 |
| B-6 | D.C. Bayonet | S6952 | 1004 | .94 | 12.8V | 200 | C-6 | 1.75" | 10 |

Miniature Incandescent Lamps

miniature lamps



D.C. Bayonet Base

S.C. Bayonet Base



Index Base

Plastic Wedge Base

S-8

Auto • Aircraft • Indicator • Marine

S6953 #88 D.C. Bayonet

S6954 #93 S.C. Bayonet

S6955 #1073 S.C. Bayonet

S6966 #1141 S.C. Bayonet

S6956 #1154 D.C. Index Base

S6895 #1156 S.C. Bay

S6896 #1156NA S.C. Bay

S6957 #1157 D.C. Index Base

S6958 #1157NA D.C. Index Base

S6959 #2057 D.C. Index Base

S6960 #2057NA D.C. Index Base

S6961 #2357 D.C. Index Base

S6962 #2357NA D.C. Index Base

S6963 #3155 Plastic Wedge

S6964 #3156 Plastic Wedge

S6965 #3157 Plastic Wedge

Packing: 10 Bulbs/Sleeve

NA=Natural Amber Color



RP-11

Auto • Lantern

S6967

#1133 S.C. Bayonet Base

Packing: 10 Bulbs/Sleeve

Not Shown Actual Size

| Bulb Type | Base | Satco Order No. | Lamp Code | Amps | Volts | Avg. Rated Hours | Filament | M.O.L. | Mst. Ctn./ Inner Pack |
|-----------|---------------|-----------------|-----------|-------|-------|------------------|----------|--------|-----------------------|
| S-8 | D.C. Bayonet | S6953 | 88 | 2.10 | 6.8V | 300 | C-6 | 2.00" | 10 |
| S-8 | S.C. Bayonet | S6954 | 93 | 1.04 | 12.8V | 700 | C-6 | 2.00" | 10 |
| S-8 | S.C. Bayonet | S6955 | 1073 | 1.8 | 12.8V | 200 | C-6 | 2.00" | 10 |
| S-8 | D.C. Index | S6956 | 1154 | 2.63 | 6.4V | 200 | C-6 | 2.00" | 10 |
| S-8 | SC. Bay | S6895 | 1156 | 2.63 | 12.8V | 1200 | C-6 | 2.00" | 10 |
| S-8 | S.C. Bay | S6896 | 1156NA | 2.63 | 12.8V | 1200 | C-6 | 2.00" | 10 |
| S-8 | D.C. Index | S6957 | 1157 | 2.1 | 12.8V | 1200 | C-6 | 2.00" | 10 |
| S-8 | D.C. Index | S6958 | 1157NA | 2.1 | 12.8V | 1200 | C-6 | 2.00" | 10 |
| S-8 | D.C. Index | S6959 | 2057 | 2.1 | 12.8V | 1200 | C-6 | 2.00" | 10 |
| S-8 | D.C. Index | S6960 | 2057NA | 2.1 | 12.8V | 1200 | C-6 | 2.00" | 10 |
| S-8 | D.C. Index | S6961 | 2357 | 2.23 | 12.8V | 400 | C-6 | 2.00" | 10 |
| S-8 | D.C. Index | S6962 | 2357NA | 2.23 | 12.8V | 400 | C-6 | 2.00" | 10 |
| S-8 | Plastic Wedge | S6963 | 3155 | 1.448 | 12.8V | 1500 | C-6 | 2.00" | 10 |
| S-8 | Plastic Wedge | S6964 | 3156 | 2.1 | 12.8V | 1200 | C-6 | 2.00" | 10 |
| S-8 | Plastic Wedge | S6965 | 3157 | 2.1 | 12.8V | 1200 | C-6 | 2.00" | 10 |
| S-8 | S.C. Bayonet | S6966 | 1141 | 1.44 | 12.8V | 1000 | C-6 | 2.00" | 10 |
| RP-11 | S.C. Bayonet | S6967 | 1133 | 3.91 | 6.1V | 200 | C-6 | 2.25" | 10 |

Miniature Xenon Lamps




| | | | |
|--|--|--|--|
| <p>T-3 1/4</p> <p>Clear/12 Volt Wedge Base</p> <p>S6968 3 Watt S6969 5 Watt</p> | <p>T-3 1/4</p> <p>Frosted/12 Volt Wedge Base</p> <p>S6972 5 Watt</p> | <p>T5</p> <p>Clear/12 Volt Wedge Base</p> <p>S6978 18 Watt</p> | <p>T5</p> <p>Frosted/12 Volt Wedge Base</p> <p>S6981 18 Watt</p> |
| <p>T-3 1/4</p> <p>Clear/24 Volt Wedge Base</p> <p>S6974 5 Watt S6975 7.5 Watt</p> <p>Packing: 10/Master</p> | <p>T-3 1/4</p> <p>Frosted/24 Volt Wedge Base</p> <p>S6976 5 Watt S6977 7.5 Watt</p> <p>Packing: 10/Master</p> | <p>T5</p> <p>Clear/24 Volt Wedge Base</p> <p>S6979 7.2 Watt S6980 10 Watt</p> <p>Packing: 10/Master</p> | <p>T5</p> <p>Frosted/24 Volt Wedge Base</p> <p>S6982 7.2 Watt S6983 10 Watt</p> <p>Packing: 10/Master</p> |

Not Shown Actual Size

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack Type | Mst. Ctn./ Inner Pack |
|-------|-----------|-------|-----------------|--------------|---------|-------|------------------|--------|----------|---------|-----------|-----------------------|
| 3 | T 3 1/4 | Wedge | S6968 | X3T3 1/4 | Clear | 12V | 20000 | 15 | C2V | 1 1/16" | Box | 10 |
| 5 | T 3 1/4 | Wedge | S6969 | X5T3 1/4 | Clear | 12V | 5000 | 33 | C2V | 1 1/16" | Box | 10 |
| 5 | T 3 1/4 | Wedge | S6974 | X5T3 1/4 | Clear | 24V | 8000 | 38 | C2V | 1 1/16" | Box | 10 |
| 5 | T 3 1/4 | Wedge | S6972 | X5T3 1/4/F | Frosted | 12V | 5000 | 33 | C2V | 1 1/16" | Box | 10 |
| 5 | T 3 1/4 | Wedge | S6976 | X5T3 1/4/F | Frosted | 24V | 8000 | 38 | C2V | 1 1/16" | Box | 10 |
| 7.5 | T 3 1/4 | Wedge | S6975 | X7.5T3 1/4 | Clear | 24V | 10000 | 65 | C2V | 1 1/16" | Box | 10 |
| 7.5 | T 3 1/4 | Wedge | S6977 | X7.5T3 1/4/F | Frosted | 24V | 10000 | 65 | C2V | 1 1/16" | Box | 10 |
| 7.2 | T5 | Wedge | S6979 | X7.2T5 | Clear | 24V | 2500 | 68 | C2R | 1 1/2" | Box | 10 |
| 7.2 | T5 | Wedge | S6982 | X7.2T5/F | Frosted | 24V | 2500 | 68 | C2R | 1 1/2" | Box | 10 |
| 10 | T5 | Wedge | S6980 | X10T5 | Clear | 24V | 2000 | 126 | C2R | 1 1/2" | Box | 10 |
| 10 | T5 | Wedge | S6983 | X10T5/F | Frosted | 24V | 2000 | 126 | C2R | 1 1/2" | Box | 10 |
| 18 | T5 | Wedge | S6978 | X18T5 | Clear | 12V | 10000 | 250 | C2R | 1 1/2" | Box | 10 |
| 18 | T5 | Wedge | S6981 | X18T5/F | Frosted | 12V | 10000 | 250 | C2R | 1 1/2" | Box | 10 |

miniature lamps

Miniature *Xenon* Lamps



T-3 1/4

Clear/12 Volt
Festoon

S6985 5 Watt
S6986 10 Watt

T-3 1/4

Clear/24 Volt
Festoon

S6987 5 Watt
S6988 10 Watt

Packing:
10/Master



T-3 1/4

Frosted/12 Volt
Festoon

S6989 5 Watt
S6990 10 Watt

T-3 1/4

Frosted/24 Volt
Festoon

S6991 5 Watt
S6992 10 Watt

Packing:
10/Master



RLX

Clear/12 Volt
Rigid Loop

S6993 5 Watt
S6994 10 Watt

RLX

Clear/24 Volt
Rigid Loop

S6995 5 Watt
S6996 10 Watt

Packing:
10/Master



RLX

Frosted/12 Volt
Rigid Loop

S6997 5 Watt
S6998 10 Watt

RLX

Frosted/24 Volt
Rigid Loop

S6999 5 Watt
S6850 10 Watt

Packing:
10/Master

| Watts | Bulb Type | Base | Satco Order No. | Lamp Code | Finish | Volts | Avg. Rated Hours | Lumens | Filament | M.O.L. | Pack Type | Mst.Ctn./ Inner Pack |
|-------|-----------|------------|-----------------|-------------|---------|-------|------------------|--------|----------|----------|-----------|----------------------|
| 5 | T 3 1/4 | D.E. Cap | S6985 | X5T3 1/4 | Clear | 12V | 20000 | 50 | C8 | 1 23/32" | Box | 10 |
| 5 | T 3 1/4 | D.E. Cap | S6987 | X5T3 1/4 | Clear | 24V | 15000 | 50 | C8 | 1 23/32" | Box | 10 |
| 5 | T 3 1/4 | D.E. Cap | S6989 | X5T3 1/4/F | Frosted | 12V | 20000 | 50 | C8 | 1 23/32" | Box | 10 |
| 5 | T 3 1/4 | D.E. Cap | S6991 | X5T3 1/4/F | Frosted | 24V | 15000 | 50 | C8 | 1 23/32" | Box | 10 |
| 10 | T 3 1/4 | D.E. Cap | S6986 | X10T3 1/4 | Clear | 12V | 20000 | 120 | C8 | 1 23/32" | Box | 10 |
| 10 | T 3 1/4 | D.E. Cap | S6988 | X10T3 1/4 | Clear | 24V | 10000 | 120 | C8 | 1 23/32" | Box | 10 |
| 10 | T 3 1/4 | D.E. Cap | S6990 | X10T3 1/4/F | Frosted | 12V | 20000 | 120 | C8 | 1 23/32" | Box | 10 |
| 10 | T 3 1/4 | D.E. Cap | S6992 | X10T3 1/4/F | Frosted | 24V | 10000 | 120 | C8 | 1 23/32" | Box | 10 |
| 5 | RLX | Rigid Loop | S6993 | 5RLX | Clear | 12V | 20000 | 45 | C8 | 1 3/4" | Box | 10 |
| 5 | RLX | Rigid Loop | S6995 | 5RLX | Clear | 24V | 20000 | 40 | C8 | 1 3/4" | Box | 10 |
| 5 | RLX | Rigid Loop | S6997 | 5RLX/F | Frosted | 12V | 20000 | 45 | C8 | 1 3/4" | Box | 10 |
| 5 | RLX | Rigid Loop | S6999 | 5RLX/F | Frosted | 24V | 20000 | 40 | C8 | 1 3/4" | Box | 10 |
| 10 | RLX | Rigid Loop | S6994 | 10RLX | Clear | 12V | 20000 | 100 | C8 | 1 3/4" | Box | 10 |
| 10 | RLX | Rigid Loop | S6996 | 10RLX | Clear | 24V | 20000 | 100 | C8 | 1 3/4" | Box | 10 |
| 10 | RLX | Rigid Loop | S6998 | 10RLX/F | Frosted | 12V | 20000 | 90 | C8 | 1 3/4" | Box | 10 |
| 10 | RLX | Rigid Loop | S6850 | 10RLX/F | Frosted | 24V | 20000 | 90 | C8 | 1 3/4" | Box | 10 |

miniature lamps

T8 Instant Start

Electronic Ballast

T8 Instant Start – Dedicated Voltage



<20% THD Electronic T8 Fluorescent Ballasts

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|--------------------|------|
| F32T8 | 1 | 120 | S6623 | QT1X32T8120/ISN/SC | 10 |
| F32T8 | 1 | 277 | S6633 | QT1X32T8277/ISN/SC | 10 |
| F32T8 | 2 | 120 | S6624 | QT2X32T8120/ISN/SC | 10 |
| F32T8 | 2 | 277 | S6634 | QT2X32T8277/ISN/SC | 10 |
| F32T8 | 3 | 120 | S6625 | QT3X32T8120/ISN/SC | 10 |
| F32T8 | 3 | 277 | S6635 | QT3X32T8277/ISN/SC | 10 |
| F32T8 | 4 | 120 | S6626 | QT4X32T8120/ISN/SC | 10 |
| F32T8 | 4 | 277 | S6636 | QT4X32T8277/ISN/SC | 10 |

Also operates F17T8 • F25T8 • F28T8/SS • F30T8/SS • F40T8 • FBO16 • FBO24 • FBO31 • FBO 32
For F40T8 operation, use 2 lamp ballast for 1 lamp, 3 lamp ballast for 2 lamps, 4 lamp ballast for 3 lamps.

| | | | | | |
|-------|-----|-----|-------|--------------|----|
| F96T8 | 1/2 | 120 | S5211 | QT2X59120/IS | 10 |
| F96T8 | 1/2 | 277 | S5212 | QT2X59277/IS | 10 |

Also Operates: FBO32, F025, FBO24, F017, FBO16, F030/SS, FBO30/SS, (30W Lamps) & F028/SS (28W Lamps)

T8 Instant Start – Universal Voltage



<10% THD Electronic T8 Fluorescent Ballasts

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|----------------------|------|
| F32T8 | 1 | 120/277 | S5207 | QTP1X32T8/UNV/ISN/SC | 10 |
| F32T8 | 2 | 120/277 | S5208 | QTP2X32T8/UNV/ISN/SC | 10 |
| F32T8 | 3 | 120/277 | S5209 | QTP3X32T8/UNV/ISN/SC | 10 |
| F32T8 | 4 | 120/277 | S5210 | QTP4X32T8/UNV/ISN/SC | 10 |

Also operates F17T8 • F25T8 • F28T8/SS • F30T8/SS • F40T8 • FBO16 • FBO24 • FBO31 • FBO32
For F40T8 operation, use 2 lamp ballast for 1 lamp, 3 lamp ballast for 2 lamps, 4 lamp ballast for 3 lamps.

| | | | | | |
|-------|---|---------|-------|----------------------|----|
| F96T8 | 2 | 120/277 | S5213 | QTP2X59T8/UNV/ISN/SC | 10 |
|-------|---|---------|-------|----------------------|----|

Also Operates: FBO32, FBO31, F025, FBO24, F017, FBO16, F030/SS, FBO30/SS (30W Lamps) & F028/SS (28W Lamps)

T8 4 Foot Programmed Start Universal Voltage



< 10% THD Electronic T8 Fluorescent Ballasts

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|---------------------|------|
| F32T8 | 1 | 120/277 | S5286 | QTP1X32T8/UNV/PSNTC | 10 |
| F32T8 | 2 | 120/277 | S5287 | QTP2X32T8/UNV/PSNTC | 10 |
| F32T8 | 3 | 120/277 | S5288 | QTP3X32T8/UNV/PSNTC | 10 |
| F32T8 | 4 | 120/277 | S5289 | QTP4X32T8/UNV/PSNTC | 10 |

Also operates F17T8 • F25T8 • F28T8/SS • F30T8/SS • FBO16 • FBO24 • FBO31 • FBO32

Also Operates: F096T8/SS (55W Lamp)

Electronic Ballasts



T5 Programmed Start Universal Voltage

T5 Programmed Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|-----------------|------|
| F28T5 | 1 | 120/277 | S5221 | QTP1X28UNVPSNNL | 20 |
| F28T5 | 2 | 120/277 | S5222 | QTP2X28UNVPSNNL | 20 |

Also operates F14T5 • F21T5 • F35T5



T5 HO Programmed Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|--|-----------------|---------|-----------------|------------------------|------|
| F39T5/HO | 1 | 120/277 | S5214 | QTP1X39/24T5HOUNVPSNNL | 20 |
| F39T5/HO | 2 | 120/277 | S5215 | QTP2X39/24T5HOUNVPSNNL | 20 |
| Also operates F24T5/HO • FPC22 • FPC40 • FT24DL • CF24DF • FT36DL • CF36DF | | | | | |
| F54T5/HO | 1 | 120/277 | S5218 | QTP1X54T5HOUNVPSNNL | 20 |
| F54T5/HO | 2 | 120/277 | S5219 | QTP2X54T5HOUNVPSNNL | 20 |
| Also operates FT55DL • FPC55 | | | | | |
| F80T5/HO | 1 | 120/277 | S5220 | QTP1X80T5HOUNVPSNNL | 20 |
| Also operates FT80DL | | | | | |



40 T12 Rapid Start

T12 F40T12 Rapid Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|----------------------|------|
| F40T12 | 1 | 120 | S5258 | QTP1X40T12/120/RSN/B | 20 |
| F40T12 | 1 | 277 | S5259 | QTP1X40T12/277/RSN/B | 20 |
| F40T12 | 2 | 120 | S5260 | QTP2X40T12/120/RSN/B | 20 |
| F40T12 | 2 | 277 | S5261 | QTP2X40T12/277/RSN/B | 20 |
| F40T12 | 3 | 120 | S5262 | QTP3X40T12/120/RSN/B | 20 |
| F40T12 | 3 | 277 | S5263 | QTP3X40T12/277/RSN/B | 20 |



Electronic Ballasts

TT5 Instant Start



TT5 FT40DL Instant Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|----------------|------|
| FT40 | 1 | 120 | S5240 | QT1x40/120/DL | 10 |
| FT40 | 1 | 277 | S5241 | QT1x40/277/DL | 10 |
| FT40 | 2 | 120 | S5242 | QT2x40/120/DL | 10 |
| FT40 | 2 | 277 | S5243 | QT2x40/277/DL | 10 |
| FT40 | 3 | 120 | S5244 | QT3x40/120/DL | 10 |
| FT40 | 3 | 277 | S5245 | QT3x40/277/DL | 10 |

Compact Fluorescent



| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|--|-----------------|---------|-----------------|-------------------------|------|
| CF13 | 1/2 | 120/277 | S5223 | OTP1/2X13CF/UNV/BS | 20 |
| CF13 | 1/2 | 120/277 | S5225 | OTP1/2X13CF/UNV/TS | 20 |
| Operates 1 or 2 each CF13DT/E • CF13DD/E | | | | | |
| CF18 | 1/2 | 120/277 | S5226 | OTP1/2X18CF/UNV/BS | 20 |
| CF18 | 1/2 | 120/277 | S5228 | OTP1/2X18CF/UNV/TS | 20 |
| Operates 1 or 2 each CF18DT/E • CF18DD/E | | | | | |
| CF26 | 1/2 | 120/277 | S5229 | OTP1/2X26CF/UNIV/BS | 20 |
| CF26 | 1/2 | 120/277 | S5231 | OTP1/2X26CF/UNIV/TS | 20 |
| Operates 1 or 2 each CF26DT/E • CF26DD/E Operates 1 each CF32DT/E • CF42DT/E | | | | | |
| CF26 | 1/2 | 120/277 | S5232 | OTP1/2XCF/UNV/BM | 20 |
| CF26 | 1/2 | 120/277 | S5233 | OTP1/2XCF/UNV/PM | 18 |
| CF26 | 1/2 | 120/277 | S5234 | OTP1/2XCF/UNV/TM | 18 |
| Operates 1 or 2 each CF26DT/E • CF26DD/E Operates 1 each CF32DT/E • CF42DT/E | | | | | |
| CF26 | 2 | 120/277 | S5235 | OTP2X26/32/42CF/UNIV/BM | 20 |
| CF26 | 2 | 120/277 | S5236 | OTP2X26/32/42CF/UNIV/PM | 18 |
| CF26 | 2 | 120/277 | S5237 | OTP2X26/32/42CF/UNIV/TM | 18 |
| Operates 2 each CF26DT/E • CF32DT/E • CF42DT/E | | | | | |
| CF57 | 1 | 120/277 | S5238 | OTP1X57CF/UNV/BM | 20 |
| CF57 | 1 | 120/277 | S5239 | OTP1X57CF/UNV/PM | 18 |
| Operates 1 each CF57DT/E • CF70DT/E | | | | | |

BS = Bottom Mount / Plastic Case
 TS = Top Mount / Plastic Case
 BM = Bottom Mount / Metal Case
 PM = PEM Stud Mount / Metal Case
 TM = Top Mount / Metal Case

T2 Universal Voltage



T2 Subminiature

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|---|-----------------|---------|-----------------|----------------|------|
| FM13 | 1/2 | 120/277 | S5246 | QT-FM | 50 |
| Operates 1 or 2 FM6 • FM8 • FM11 • FM13 | | | | | |

Magnetic Ballasts

Rapid Start

F40T12 & F34T12 Rapid Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|---|-----------------|---------|-----------------|----------------|------|
| F34T12 | 1 | 120 | S5274 | MB1X40/120RS | 10 |
| F34T12 | 1 | 277 | S5275 | MB1X40/277RS | 10 |
| Also operates F40T12 • F40T10 • FB40T12 • FB34T12/SS • F30T12 • F25T12/SS | | | | | |
| F34T12 | 2 | 120 | S6620 | MB2X40/120RS | 10 |
| F34T12 | 2 | 277 | S6622 | MB2X40/277RS | 10 |
| Also operates F40T12 • F40T10 • FB40T12 • FB34T12/SS | | | | | |
| F40T12 | 1 | 120 | S5276 | MB1X40/120RES | 16 |
| Operates F40T12 FULL WATTAGE LAMPS ONLY - Not for use for F34T12 lamps | | | | | |
| F30T12 | 2 | 120 | S5171 | MB2X30/120RS | 10 |
| F30T12 | 2 | 277 | S5170 | MB2X30/277RS | 10 |
| Operates F30T12 and F25T12/SS Lamps | | | | | |



Instant Start Slimline

T12 Slimline Instant Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|---|-----------------|---------|-----------------|----------------|------|
| F48T12 | 2 | 120 | S5277 | MB2X48/120IS | 6 |
| F48T12 | 2 | 277 | S5278 | MB2X48/277IS | 6 |
| Also operates F48T12/SS | | | | | |
| F96T12 | 1 | 120 | S5279 | MB1X96/120IS | 6 |
| F96T12 | 1 | 277 | S5280 | MB1X96/277IS | 6 |
| F96T12 | 2 | 120 | S6621 | MB2X96/120IS | 6 |
| F96T12 | 2 | 277 | S5281 | MB2X96/277IS | 6 |
| Also operates F60T12 • F64T12 • F72T12 • F84T12 • F96T12/SS | | | | | |



Preheat/Trigger Start

T8 / T12 PreHeat and Trigger Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|---|-----------------|---------|-----------------|-----------------|------|
| F15T12 | 1 | 120 | S5268 | MB1X15/120PH/TP | 16 |
| F20T12 | 1 | 120 | S5269 | MB1X20/120PH/TP | 40 |
| F20T12 | 1 | 120 | S5270 | MB1X20/120PH | 40 |
| F20T12 | 2 | 120 | S5271 | MB2X20/120PH/TP | 16 |
| Also operates F14T8 • F14T12 • F15T8 • F15T12 | | | | | |

TP = Thermal Protection



Magnetic

Ballasts

Circline



T9 Circline Rapid Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|----------------|------|
| FC8T9 | 1 | 120 | S5273 | MB1X22/120CIRC | 16 |
| FC12T9 | 1 | 120 | S5272 | MB1X32/120CIRC | 16 |

Also operates FC16T9

Rapid Start HO



T12 HO Rapid Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|----------------|------|
| F96T12/HO | 1 | 120 | S5282 | MB1X96HO/120RS | 4 |
| F96T12/HO | 1 | 277 | S5283 | MB1X96HO/277RS | 4 |
| F96T12/HO | 2 | 120 | S5284 | MB2X96HO/120RS | 4 |
| F96T12/HO | 2 | 277 | S5285 | MB2X96HO/277RS | 4 |

Also operates F24HO • F36HO • F42HO • F48HO • F60HO • F72HO • F84HO • F96HO/SS

Rapid Start VHO



T12 VHO Rapid Start

| Primary Lamp Type | Number of Lamps | Voltage | Satco Order No. | Ballast Number | Case |
|-------------------|-----------------|---------|-----------------|------------------|------|
| F96T12/VHO | 1 | 120 | S5264 | MB1X96/VHO/120RS | 4 |
| F96T12/VHO | 1 | 277 | S5265 | MB1X96/VHO/277RS | 4 |

Also operates F48/VHO • F60/VHO • F72/VHO • F96/VHO/SS

| | | | | | |
|------------|---|-----|-------|------------------|---|
| F96T12/VHO | 2 | 120 | S5266 | MB2X96/VHO/120RS | 4 |
| F96T12/VHO | 2 | 277 | S5267 | MB2X96/VHO/277RS | 4 |

Also operates F72/VHO • F96/VHO/SS

Socket Ballasts Twist-Lock



Socket Ballasts

- Finish: Ivory
- Rating: 120V/60HZ
- CUL Listed
- Rated: Indoor / Outdoor
Minus 20 Degrees
- Replaceable
- Detachable:
Twist Lock Socket



13/18/26W
Standard



13/18/26W Uno Ring
Standard with Uno Ring

80-1325 13W
80-1324 18W
80-1383 26W

80-1335 13W
80-1336 18W
80-1382 26W



26/32/42W
Multi-Wattage



26/32W/Dimming
Multi-Wattage



13/18/26W
Low Profile

80-1323

80-1331
• Integral Harp Saddle
• Integral Dimmer
• Indoor Only

80-1384 13W
80-1385 18W
80-1386 26W

| Primary Lamp Type | Satco OrderNo. | Finish | Terminal | Cap | Hickey | Wire | Pkd |
|-------------------|----------------|--------|----------------|-----|--------|--------|-----|
| 13W | 80/1325 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 18W | 80/1324 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 26W | 80/1383 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 13W Uno / Ring | 80/1335 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 18W Uno / Ring | 80/1336 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 26W Uno / Ring | 80/1382 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 26/32/42 W | 80/1323 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 26/32 Dimmer | 80/1331 | Ivory | With 36" Leads | Cap | Hickey | UL1015 | 200 |
| 13W Small | 80/1384 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 18W Small | 80/1385 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |
| 26W Small | 80/1386 | Ivory | With 24" Leads | Cap | Hickey | UL1015 | 200 |

SATCO BULB CHANGERS

The easy way to change hard to reach bulbs. Available in PAR, incandescent and R type changers.

Not Shown
Actual Size



Incandescent
Bulb Changer
S70-0101



Par Type
Bulb Changer
S70-3001



R Type
Bulb Changer
S70-3002



90-1310

Brass Finish
Light Bulb Cage
(for use with 90-445
keyless receptacle)



92-324

Medium to Medium
Porcelain
Extender
Overall Ext. 1"



92-323

Medium to Medium
Bakelight
Extender
Overall Ext. 1"



8-24 Ft. ▶

Alumiglass Extension Pole

S70-6624

Two section handle,
threaded end fits
all changers.
Professional quality.

8-16 Ft. ▶

Alumiglass Extension Pole

S70-6516

Two section handle,
threaded end fits
all changers.
Professional quality.

Note: For standard
ceilings, broomstick
handle will fit changers.

◀ 6-12 Ft.

Aluminum Extension Pole

S70-9272

Two section handle,
"nylon" threaded,
fits all changers.
Homeowner quality.



accessories



S1352 Four foot display canopy

22" D X 48" W X 10" H

The bold colors and contemporary graphics of this dynamic header create a sophisticated product presentation. The 22" X 48" bottom Chrome louver allows light to pass through for product illumination.

Mounts to any standard four foot gondola display.

Four Color Retail Packaging

offers ease of product identification, uniformity and contemporary design.

Many of our items are packaged in four color inner cartons. These multi-packs can be stacked out for promotional purposes creating additional sales!



merchandising





Satco Light Bulbs - A brand consumers have purchased with confidence for over 40 years.



merchandising

*S1300 A - Four foot white gondola display. (Bottom shelf included)
48"W X 24"D X 71"H*

S1300 B - (3) Four foot white shelves





Satco Power Panels can be mounted on the end of a gondola display or hung on a wall.

merchandising



S1360 *Decorative light bulb power panel:*

- 10 - S3774 10 - S3786
- 10 - S3782 10 - S3732
- 10 - S3778 10 - S3735
- 10 - S3785 10 - S3762
- 10 - S3731 10 - S3784
- 10 - S3734 10 - S3763
- 10 - S3775 10 - S3787
- 10 - S3783 10 - S3793
- 10 - S3779 10 - S3796

15"W X 48"H X 4.5"D



S1361 *Appliance light bulb power panel:*

- 10 - S3708 20 - S3724
- 10 - S3712 20 - S3797
- 20 - S3720 10 - S3711
- 20 - S3723 10 - S3703
- 20 - S3792 20 - S3729
- 10 - S3709 20 - S3791
- 10 - S3702 20 - S3794
- 20 - S3721

15"W X 48"H X 4.5"D



S1362 *Halogen light bulb power panel:*

- 12 - S3459 12 - S3486
- 12 - S3468 12 - S3432
- 12 - S3469 12 - S3488
- 12 - S3465 12 - S3489
- 12 - S3467 12 - S3431
- 12 - S3425 12 - S3496
- 12 - S3461 12 - S3497
- 12 - S3462 12 - S3480
- 12 - S3463 12 - S3481
- 12 - S3484 12 - S3423
- 12 - S3485

15"W X 48"H X 4.5"D

Halogen Light Bulb Center 2' MERCHANDISING PROGRAM

- Self Stocking Display Unit
 - High Impact Graphics & Packaging
 - Adjustable Shelves
 - Uses Only 2'X2' Floor Space
 - Features; Soft Ray Glare Free MR16 & PAR Lamps
- Plus Other Halogen Up Sell Products

#HAL/2FT/DISP

Counter Top Demonstrator Display



S1410 Soft Ray demonstrator

Interactive display unit compares a standard halogen lamp to a Soft Ray frosted PAR

14 1/2" W X 13 3/4" D X 18 1/2" H



Halogen Light Bulb Center:

| | | |
|------------|------------|------------|
| 6 - S4603 | 24 - S4503 | 15 - S4103 |
| 6 - S4600 | 24 - S4504 | 15 - S4104 |
| 6 - S4601 | 12 - S4120 | 15 - S4105 |
| 6 - S4602 | 12 - S4121 | 15 - S4106 |
| 12 - S4500 | 12 - S4122 | 15 - S4107 |
| 12 - S4501 | 12 - S4123 | 1 - S4150 |
| 12 - S4502 | 15 - S4100 | 1 - S4152 |
| 12 - S4505 | 15 - S4101 | |
| 12 - S4506 | 15 - S4102 | |

Actual Dimensions: 27" W X 76" H



SATCO'S

POINT of PURCHASE
DISPLAYS are the perfect tool to assist in the promotion of Satco brand lighting products.

Energy Saving Light Bulb Center

2' MERCHANDISING PROGRAM

- Self Stocking Display Unit
- High Impact Graphics & Packaging
- Adjustable Shelves
- Uses Only 2'X2' Floor Space
- Features; Energy Star Certified Products

#CFL/2FT/DISP



Energy Saving Light Bulb Center:

| | | |
|-------------|-------------|------------|
| 12 - S6202* | 12 - S6214* | 6 - S6244 |
| 12 - S6203* | 12 - S6215* | 12 - S6245 |
| 12 - S6204* | 6 - S6216* | 6 - S6253 |
| 6 - S6210 | 6 - S6217 | 6 - S6254 |
| 6 - S6211* | 6 - S6218* | 1 - S1415 |
| 6 - S6212* | 6 - S6222 | 1 - S1453 |
| 12 - S6213* | 12 - S6243 | |

Actual Dimensions: 27" W X 76" H

Light Bulb Center

2' MERCHANDISING PROGRAM

- Self Stocking Display Unit
- High Impact Graphics & Packaging
- Adjustable Shelves
- Uses Only 2'X2' Floor Space

#GEN/2FT/DISP

Light Bulb Center:

| | |
|------------|------------|
| 48 - S1711 | 24 - S2808 |
| 48 - S1712 | 24 - S2809 |
| 48 - S1713 | 12 - S4421 |
| 48 - S1714 | 12 - S4426 |
| 48 - S1810 | 24 - S2853 |
| 48 - S1811 | 24 - S2854 |
| 48 - S1812 | 24 - S2855 |
| 36 - S1820 | 20 - S3791 |
| 36 - S1821 | 20 - S3792 |
| 24 - S3938 | 20 - S3729 |
| 12 - S3440 | 20 - S3724 |
| 12 - S3441 | 20 - S3720 |
| 12 - S3442 | 20 - S3721 |
| 12 - S3443 | 10 - S3703 |
| 12 - S3447 | 10 - S3705 |
| 12 - S3448 | 10 - S3778 |
| 12 - S3449 | 10 - S3779 |
| 24 - S3204 | 10 - S3754 |
| 24 - S3211 | 10 - S3728 |

Actual Dimensions: 27" W X 76" H



Decorative Bulb Displays

- Gravity feed bulb dispenser
- Stocks 24 different styles
- Compact size
- Versatile merchandising options
- Contemporary design
- Easy product identification



S-101 Wall mounted decorative light bulb display.

Stocks the same product selection as the S-100 merchandiser.

45"L X 27"H X 6.6"D




Rotating Display can be used free standing, or countertop

S-100 DISPLAY

This self-standing floor or counter display takes up less than 2sq. ft. of space.

S-100 display consists of rack and 25ea. of:
 S3231, S3232, S3234, S3235, S3262, S3263, S3273,
 S3274, S3275, S3277, S3278, S3279, S3282, S3283,
 S3284, S3285, S3286, S3287, S3293, S3296, S3822,
 S3823, S3825 & S3826

Floor display 66" H.



Counter display 40" H.

Light Bulb Center Promotional Signs

Hanging and Window

S1462 Hanging
3-Way Sign
Includes; string and hook
for hanging



S1461 Window/Hanging
2-Way Signs
Includes; string, hook & suction cups
for hanging and window use