

# Product Supplement

June 2011









# Table of Contents

Bravo.....	2
Joy.....	6
Adorn Bath.....	11
Close-to-ceiling.....	12
Fan Light Kits.....	12
Mac Outdoor.....	13
Index.....	Back Cover

# Bravo

---

A current, truly transitional style is achieved with Bravo's free-flowing arms that are gracefully suspended with fluted shaped glass shades. Bravo is available in an Antique Bronze finish with etched amber linen shades or white etched glass shades with a Brushed Nickel finish.

## THREE-LIGHT CHANDELIER

**P4621-09** Brushed Nickel

**P4621-20** Antique Bronze

Size: 23" dia., 20-1/8" ht. Overall ht. w/chain 95"; wire 12'.

Lamps: Three medium base lamps, each 100w max.



P4621-20



P4621-09

## FOUR-LIGHT CHANDELIER

**P4622-09** Brushed Nickel

**P4622-20** Antique Bronze

Size: 24" dia., 21" ht. Overall ht. w/chain 96"; wire 12'.

Lamps: Four medium base lamps, each 100w max.



P4622-09



P4622-20





P4623-09



P4623-20

**FIVE-LIGHT CHANDELIER**  
**P4623-09** Brushed Nickel  
**P4623-20** Antique Bronze  
Size: 27" dia., 23" ht. Overall ht. w/chain 97"; wire 12'.  
Lamps: Five medium base lamps, each 100w max.



P4625-09



P5300-09



P5300-20

**MINI-PENDANT**  
**P5300-09** Brushed Nickel  
**P5300-20** Antique Bronze  
Chain- or stem-hung mini-pendant. Includes 6' of chain and two 6" stems.  
Size: 7-1/4" dia., 6-1/2" ht. Overall ht. w/chain or stem 94"; wire 10'.  
Lamp: One medium base lamp, 100w max.

**NINE-LIGHT CHANDELIER**  
**P4625-09** Brushed Nickel  
**P4625-20** Antique Bronze  
Two-tier.  
Size: 32" dia., 31" ht. Overall ht. w/chain 106"; wire 12'.  
Lamps: Nine medium base lamps, each 100w max.

# Bravo

## THREE-LIGHT FOYER

**P3821-09** Brushed Nickel

**P3821-20** Antique Bronze

Size: 18" dia., 21-1/2" ht. Overall  
ht. w/chain 96"; wire 12'.

Lamps: Three candelabra base  
lamps, each 60w max.



## THREE-LIGHT FOYER

**P3912-09** Brushed Nickel

**P3912-20** Antique Bronze

Size: 21" dia., 23-1/2" ht.

Overall ht. w/chain 98";

wire 12'.

Lamps: Three medium base  
lamps, each 100w max.



# Bravo Bath



Product No.	Finish	Description	Size	Lamp(s)
<b>P2004-09</b>	Brushed Nickel	One-light	7-1/4" W., 9" ht.	1 medium base,
<b>P2004-20</b>	Antique Bronze		H/CTR 4-1/2".	100w max.
			Extends 8-3/4".	
<b>P2005-09</b>	Brushed Nickel	Two-light	17" W., 8-1/2" ht.	2 medium base,
<b>P2005-20</b>	Antique Bronze		H/CTR 6-1/8".	each 100w max.
			Extends 8-3/4".	
<b>P2006-09</b>	Brushed Nickel	Three-light	26-3/4" W., 8-3/4" ht.	3 medium base,
<b>P2006-20</b>	Antique Bronze		H/CTR 6-3/8".	each 100w max.
			Extends 8-3/4".	
<b>P2007-09</b>	Brushed Nickel	Four-light	37-1/4" W., 9" ht.	4 medium base,
<b>P2007-20</b>	Antique Bronze		H/CTR 6-1/2".	each 100w max.
			Extends 8-3/4".	



P2005-20

All fixtures on these pages mount up or down.

# Joy

With sophisticated design styling, Joy features voluminous curves for a soft and stylish profile. Etched light amber glass shades in an Antique Bronze finish or white etched glass shades with a Brushed Nickel finish complement the fashion-forward frame.

This collection comes with two 6" stems and one standard chain, which can be hung and showcased on a variety of ceilings.

## THREE-LIGHT CHANDELIER

**P4489-09** Brushed Nickel

**P4489-20** Antique Bronze

Chain- or stem-hung chandelier. Includes 6' of chain and two 6" stems.

Size: 20" dia., 16-3/8" ht. Overall ht. w/chain or stem 103"; wire 12'.

Lamps: Three medium base lamps, each 100w max.



## MINI-PENDANT

**P5270-09** Brushed Nickel

**P5270-20** Antique Bronze

Chain- or stem-hung mini-pendant. Includes 6' of chain and two 6" stems.

Size: 6" dia., 7" ht. Overall ht. w/chain or stem 94"; wire 10'.

Lamp: One medium base lamp, 100w max.





P4490-20



**FIVE-LIGHT CHANDELIER**  
**P4490-09** Brushed Nickel  
**P4490-20** Antique Bronze  
Chain- or stem-hung chandelier.  
Includes 6' of chain and two 6"  
stems.  
Size: 24" dia., 18-7/8" ht. Overall  
ht. w/chain or stem 105"; wire 12'.  
Lamps: Five medium base lamps,  
each 100w max.

P4490-20



P4490-09



P4490-09



# Joy

## THREE-LIGHT FOYER

**P3587-09** Brushed Nickel

**P3587-20** Antique Bronze

Chain- or stem-hung foyer.

Includes 6' of chain and two 6" stems.

Size: 14-5/8" dia., 17" ht. Overall ht. w/chain or stem 104"; wire 12'.

Lamps: Three candelabra base lamps, each 60w max.





P4492-09



P4492-09

**NINE-LIGHT CHANDELIER**

**P4492-09** Brushed Nickel

**P4492-20** Antique Bronze

Two-tier. Chain- or stem-hung chandelier. Includes 6' of chain and two 6" stems.

Size: 28" dia., 27-3/4" ht. Overall ht. w/chain or stem 115"; wire 15'. Lamps: Nine medium base lamps, each 100w max.



P4492-20



P4492-20

# Joy Bath



P2000-20



P2002-20



P2001-20



P2003-20



P2000-09



P2002-09



P2001-09



P2003-09

Product No.	Finish	Description	Size	Lamp(s)
P2000-09	Brushed Nickel	One-light	6" W., 9-1/2" ht.	1 medium base,
P2000-20	Antique Bronze		H/CTR 6".	100w max.
			Extends 7".	
P2001-09	Brushed Nickel	Two-light	14" W., 7-5/8" ht.	2 medium base,
P2001-20	Antique Bronze		H/CTR 4-1/8".	each 100w max.
			Extends 8-1/8".	
P2002-09	Brushed Nickel	Three-light	22" W., 7-5/8" ht.	3 medium base,
P2002-20	Antique Bronze		H/CTR 4-1/8".	each 100w max.
			Extends 8-1/8".	
P2003-09	Brushed Nickel	Four-light	30" W., 7-5/8" ht.	4 medium base,
P2003-20	Antique Bronze		H/CTR 4-1/8".	each 100w max.
			Extends 8-1/8".	

All fixtures on these pages mount up or down.





# Adorn Bath

Created to easily coordinate with the Janos, Joy and Bravo families, Adorn features fluted glass shades that mount up or down on a curving frame.

Offered in a Brushed Nickel finish with etched glass or an Antique Bronze finish with etched light amber glass.



P2010-09



P2008-09



P2011-09



P2009-09



P2009-20



P2008-20



P2011-20

Product No.	Finish	Description	Size	Lamp(s)
P2008-09	Brushed Nickel	One-light	5-1/4" W., 6-3/4" ht.	1 medium base ,
P2008-20	Antique Bronze		H/CTR 3-3/8".	100w max.
			Extends 7".	
P2009-09	Brushed Nickel	Two-light	13-1/4" W., 6-5/8" ht.	2 medium base,
P2009-20	Antique Bronze		H/CTR 4-3/8".	each 100w max.
			Extends 6-1/4".	
P2010-09	Brushed Nickel	Three-light	21-1/2" W., 6-5/8" ht.	3 medium base,
P2010-20	Antique Bronze		H/CTR 4-3/8".	each 100w max.
			Extends 7-1/2".	
P2011-09	Brushed Nickel	Four-light	28-1/4" W., 6-5/8" ht.	4 medium base,
P2011-20	Antique Bronze		H/CTR 4-3/8".	each 100w max.
			Extends 7-1/2".	



P2010-20

# Fan Light Kits

**P2646-09** Brushed Nickel

**P2646-20** Antique Bronze

**P2646-30** White

Universal-style light kit with quick-connect wiring. Adjustable metal shade with black baffle.

Size: 9" dia. (adjustable to 11" dia.), 6-5/8" ht.

Lamps: Three medium base CFL lamps included, each 13w max.

Non-dimmable.



P2646-20



P2646-09



P2646-30

# Close-to-ceiling



P3408-20T

## ONE-LIGHT CLOSE-TO-CEILING

**P3408-20T** Antique Bronze

Size: 7-1/2" dia., 4-7/8" ht.

Lamp: One medium base lamp, 60w max.



P3410-20T

## TWO-LIGHT CLOSE-TO-CEILING

**P3410-20T** Antique Bronze

Size: 9-1/2" dia., 5-1/4" ht.

Lamps: Two medium base lamps, each 60w max.



P3412-20T

## TWO-LIGHT CLOSE-TO-CEILING

**P3412-20T** Antique Bronze

Size: 11-3/4" dia., 6" ht.

Lamps: Two medium base lamps, each 75w max.

# Mac

---

With essential back-to-basics design styling, Mac outdoor lanterns feature a classic Arts and Crafts-inspired profile that is ideal for many home exteriors, from lodge to bungalow. A durable textured Black powder coat finish, cast aluminum construction and clear water glass accentuates the simplified design.



P5906-31

**P5906-31** Black  
One-light wall lantern.  
Size: 6" sq., 8-1/2" ht.  
Extends 7-1/8".  
Lamp: One medium base  
lamp, 100w max.



P5907-31

**P5907-31** Black  
One-light wall lantern.  
Size: 8-3/4" sq., 12-1/4" ht.  
Extends 10-1/8".  
Lamp: One medium base  
lamp, 100w max.





Progress Lighting, Inc.

701 Millennium Boulevard  
Greenville, SC 29607  
www.progresslighting.com

6/11

# Index

---

P2000	10
P2001	10
P2002	10
P2003	10
P2004	5
P2005	5
P2006	5
P2007	5
P2008	11
P2009	11
P2010	11
P2011	11
P2646	12
P3408	12
P3410	12
P3412	12
P3587	8
P3821	4
P3912	4
P4489	6
P4490	7
P4492	9
P4621	2
P4622	2
P4623	3
P4625	3
P5270	6
P5300	3
P5906	13
P5907	13



Hubbell Lighting, Inc.