

Product Supplement



January 2012





Table of Contents

Bingo.....	2	Fortune Bath.....	63
Nissé.....	4	Orbitz Bath.....	63
Calven.....	6	Fan Light Kits.....	64
Cuddle.....	8	Hoop.....	65
Dibs.....	10	Peek-a-Boo.....	65
Divot.....	12	Coupe.....	66
Rock-on.....	14	Greeting.....	67
Ashbury.....	14	Bay Court Outdoor.....	68
Joy.....	16	Welcome.....	70
Bay Court.....	21	Regatta.....	71
Haven.....	21	Merit.....	72
Alexa.....	22	MAC.....	73
Rave.....	24	Soul.....	73
Bravo.....	28	Reside.....	74
Gather.....	31	Pedigree.....	75
Heart.....	34	Resort.....	76
Moments.....	38	Imperial.....	77
Orbitz.....	40	Enchant.....	78
Caress.....	43	Lamps.....	79
LadyLuck.....	46	Index.....	80
Fortune.....	48		
Inspire.....	50		
Close-to-Ceiling.....	53		
Sconces.....	53		
Nissé Bath.....	54		
Calven Bath.....	55		
Joy Bath.....	56		
Bravo Bath.....	57		
Gather Bath.....	58		
Alexa Bath.....	59		
Adorn Bath.....	60		
Addison Bath.....	61		
Inspire Bath.....	62		

Bingo

Circular forms serve as wall or ceiling art. Bingo features a distressed mirror surface, an ironwork frame and etched opal acrylic diffusers.

Available in -09 Brushed Nickel and -74 Venetian Bronze finishes.



P3957-09
shown ceiling-mounted



P3957-74
shown ceiling-mounted



P3957-09
shown wall-mounted

P3957-09 Brushed Nickel
P3957-74 Venetian Bronze
Wall and ceiling mount.
Size: 45-3/4" L., 24" W. 3-1/2" ht.
Lamps: Five circline lamps,
each 22w max.
ADA

Bingo

P3956-09 Brushed Nickel
P3956-74 Venetian Bronze
Wall and ceiling mount.
Size: 40" L., 11-5/8" W. 3-3/8" ht.
Lamps: Six GU24 base CFL lamps,
each 13w max.
ADA



P3956-09
shown ceiling-mounted



P3956-74
shown ceiling-mounted



P3958-09
shown ceiling-mounted

P3958-74
shown wall-mounted



P3958-09 Brushed Nickel
P3958-74 Venetian Bronze
Wall and ceiling mount.
Size: 24" L., 23-3/4" W., 3-3/8" ht.
Lamps: Three circline lamps, each
22w max.
ADA





Nissé

Cosmopolitan glamour with a vintage modern feel. Sweeping, square arms and sparkling, optical prisms.

Vanity and small mini-pendant features oval, opal etched glass shades.

New pendants feature clear acrylic rod diffusers, lustrous silver chiffon shades.

Available in -104 Polished Nickel finish.

All Nissé stem-hung fixtures include one 6", four 12" stems and 6 links of chain.

See pages 11-13 for coordinating Nissé fixtures.

TWO-LIGHT FOYER PENDANT

P3938-104 Polished Nickel
Silver chiffon shade surrounded by clear acrylic rods.
Size: 15-1/8" dia., 27-3/4" ht.
Overall ht. w/chain 91"; wire 120".
Lamps: Two medium base lamps, each 75w max.



P3938-104



P4629-104

FIVE-LIGHT CHANDELIER
P4629-104 Polished Nickel
Opulent beads, clear glass discs and white linen shade.
Size: 24" dia., 32" ht. Overall ht. w/chain 107"; wire 180".
Lamps: Five candelabra base lamps, each 60w max.

MINI-PENDANT

P5105-104 Polished Nickel
Silver chiffon shade surrounded by clear acrylic rods.
Size: 6" dia., 7-3/8" ht. Overall ht. w/chain or stem 72"; wire .
Lamp: One medium base lamp, 100w max.



P5105-104



P5019-104



P5019-104

OVAL MINI-PENDANT
P5019-104 Polished Nickel
Opal glass with clear glass disc.
Size: 5-1/2" L., 3-1/2" W., 6-7/8" ht. Overall ht. w/stem 73"
Lamp: One medium base lamp, 100w max.

Calven

Bold, graphic lines and architectural details highlight the etched opal etched glass in the Calven collection. A sculptural profile complemented by oversized opal linen shades.

Features -80 Forged Black and new -09 Brushed Nickel finishes

All Calven hanging fixtures include two 6", one 12" and two 15" stems and 6 links of chain.

See Progress Catalog 129 pages 40-41 for Calven in -80 finish.



P3878-09

THREE-LIGHT CONVERTIBLE

P3878-09 Brushed Nickel

Stem and ceiling mounts both included.

Size: 16" dia., 10-1/4" ht. Overall ht. w/stem 75"; wire 10'.

Lamps: Three medium base lamps, each 100w max.



P3878-09



P5118-09WB

MINI-PENDANT

P5118-09WB Brushed Nickel

Size: 6-3/8" dia., 10-3/4" ht. Overall ht. w/stem 75"; wire 120".

Lamp: One G9 base halogen lamp, 60w max. included.



P3937-09

TWO-LIGHT FOYER

P3937-09 Brushed Nickel

P3937-80 Forged Black

-80 has linen shade and -09 has glass shade.

Size: 16" dia., 28" ht. Overall ht. w/stem 94"; wire 180".

Lamps: Two medium base lamps, each 60w max.



P3937-80

Calven



P4537-09

THREE-LIGHT CHANDELIER
P4537-09 Brushed Nickel
Size: 25" dia., 26" ht. Overall ht. w/stem 90"; wire 10'.
Lamps: Three candelabra base G-16-1/2 lamps, each 60w max.



P4539-09

FIVE-LIGHT CHANDELIER
P4539-09 Brushed Nickel
Size: 30" dia., 31" ht. Overall ht. w/stem 95"; wire.
Lamps: Five candelabra base G-16-1/2 lamps, each 60w max.



P5004-09

THREE-LIGHT PENDANT
P5004-09 Brushed Nickel
Size: 18" dia., 32-7/8" ht. Overall ht. w/stem 97"; wire 10'.
Lamps: Three medium base lamps, each 100w max.



P3209-09WB

WALL BRACKET
P3209-09WB Brushed Nickel
Size: 6-3/8" W, 11" ht. Extends 7-5/8".
Lamp: One G9 base halogen lamp, 60w max. included

Cuddle

Cuddle is comprised of a sculptural play of intersecting ovals. An oval frame embraces the layered oval shade. Mylar exterior shade with linen interior shade. Incandescent and fluorescent options.

-20 Antique Bronze and -09 Brushed Nickel finishes

All fixtures come with one 6", four 12" stems and 6 links of chain.

SIX-LIGHT PENDANT
P5049-09 Brushed Nickel
P5049-20 Antique Bronze
Size: 42" L., 8" W., 26-1/2" ht.
Overall ht. w/stem 93";
wire 180".
Lamps: Six candelabra base
lamps, each 60w max.

P5049-09
P5049-09EBWB



TWO-LIGHT CFL PENDANT
P5049-09EBWB Brushed Nickel
P5049-20EBWB Antique Bronze
Size: 42" L., 8" W., 26-1/2" ht.
Overall ht. w/chain 93";
wire 180".
Lamps: Two 42w GU24 CFL
lamps, included.

P5049-20
P5049-20EBWB



Cuddle



P5059-20
P5059-20EBWB



P5059-09
P5059-09EBWB

TWO-LIGHT PENDANT
P5059-09 Brushed Nickel
P5059-20 Antique Bronze
Size: 11" L., 6-1/2" W., 13" ht.
Overall ht. w/chain 79";
wire 180".
Lamps: Two candelabra base
lamps, each 60w max.

ONE-LIGHT CFL PENDANT
P5059-09EBWB Brushed Nickel
P5059-20EBWB Antique Bronze
Size: 11" dia., 13" ht. Overall ht.
w/chain 79"; wire 180".
Lamps: One 18w GU24 squat
CFL lamp, included.



P5058-09
P5058-09EBWB

FOUR-LIGHT PENDANT
P5058-09 Brushed Nickel
P5058-20 Antique Bronze
Size: 24" L., 7" W., 21" ht.
Overall ht. w/chain 87";
wire 180".
Lamps: Four candelabra base
lamps, each 60w max.



P5058-20
P5058-20EBWB

TWO-LIGHT CFL PENDANT
P5058-09EBWB Brushed Nickel
P5058-20EBWB Antique Bronze
Size: 24" L., 7" W., 21" ht.
Overall ht. w/chain 87";
wire 180".
Lamps: Two 26w GU24 squat
CFL lamps, included.



Dibs

Square etched opal glass shades, which are suspended by rectilinear framework. A fashion forward, unique design.

Available in -09 Brushed Nickel finish.

All Dibs hanging fixtures come with one 6", four 12" stems and 6 links of chain.



P7027-09WB




P7027-09WB

ONE-LIGHT WALL SCONCE

P7027-09WB Brushed Nickel
Size: 7" W., 13" ht. Extends
7-1/2". H/CTR 7-1/8".


Lamp: One G9 base halogen
lamp, 60w max., included.





P3943-09WB

FOUR-LIGHT SEMI-FLUSH
P3943-09WB Brushed Nickel
Can be stem or flush mount
Size: 12-1/8" sq., 11" ht.
Lamps: Four G9 base halogen lamps, each 60w max., included.



P3943-09WB



P3968-09WB

FOUR-LIGHT FOYER
P3968-09WB Brushed Nickel
Size: 16-1/2" sq., 20-3/4" ht.
Overall ht. w/stem 86";
wire 180".
Lamps: Four G9 base halogen lamps, each 60w max., included.



P5126-09WB

MINI-PENDANT
P5126-09WB Brushed Nickel
Size: 7" sq., 13-1/4" ht. Overall
ht. w/stem 78"; wire 120".
Lamp: One G9 base halogen lamp, 60w max., included.

Divot

Handcrafted sophisticated European design. K9 glass oblong accents and center column. Opal etched mouth-blown shades with concave, divot profile on bottom of the glass.

Available in -09 Brushed Nickel finish.

All Divot hanging fixtures come with one 6", four 12" stems and 6 links of chain.

FIVE-LIGHT CHANDELIER

P4649-09WB Brushed Nickel
Size: 26" dia., 20-1/2" ht. Overall ht. w/chain 87"; wire 180".
Lamps: Five G9 base halogen lamps, each 60w max., included.



FOUR-LIGHT LINEAR CHANDELIER

P4648-09 Brushed Nickel
Size: 35-3/4" L., 15" W. 8-3/8" ht. Overall ht. w/stem 74"; wire 180".
Lamps: Four medium base lamps, each 100w max.



MINI-PENDANT

P5129-09WB Brushed Nickel
Size: 7" dia., 17-3/4" ht. Overall ht. w/stem 82"; wire 180".
Lamp: One G9 base halogen lamp, 60w max., included.

Divot



P3798-09

TWO-LIGHT SEMI-FLUSH

P3798-09 Brushed Nickel
Size: 15-5/8" dia., 6-1/8" ht.
Lamps: Two medium base lamps, each 75w max.



P5062-09

THREE-LIGHT PENDANT

P5062-09 Brushed Nickel
Size: 15" dia., 19" ht. Overall ht. w/stem 84"; wire 180".
Lamps: Three medium base lamps, each 100w max.



P3948-09

FOUR-LIGHT PENDANT

P3948-09 Brushed Nickel
Size: 22-3/8" dia., 22-3/4" ht.
Overall ht. w/stem 89"; wire 180".
Lamps: Four medium base lamps, each 100w max.



Rock-on

Smooth etched glass with Copper Bronze finish.

See page 32 of Progress Catalog 129 for matching Rock-on fixtures.

MINI-PENDANT

P5164-124WB Copper Bronze
Includes one 6", four 12" stems and 6 links of chain.

Size: 4-3/4" dia., 8" ht. Overall ht. w/chain or stem 73"; wire 120".

Lamp: One candelabra base lamp, 60w max., included.



Ashbury

Unique double drum shade highlighted by Silver Ridge finish and etched bottom diffuser.

See pages 20-21 of Progress Catalog 129 for matching Ashbury fixtures.



THREE-LIGHT FOYER

P3932-134 Silver Ridge
Size: 18" dia., 35-1/2" ht. Overall ht. w/chain 111"; wire 120".
Lamps: Three medium base lamps, each 100w max.



P4463-134 Oval Chandelier from the Ashbury Collection

Joy

With sophisticated design styling, Joy features voluminous curves for a soft and stylish profile. Etched light amber glass shades in an Antique Bronze finish or white etched glass shades with a Brushed Nickel finish complement the fashion-forward frame.

This collection comes with two 6" stems and one standard chain, which can be hung and showcased on a variety of ceilings.

THREE-LIGHT CHANDELIER

P4489-09 Brushed Nickel

P4489-20 Antique Bronze

Chain- or stem-hung chandelier.

Includes 6' of chain and two 6" stems.

Size: 20" dia., 16-3/8" ht. Overall ht. w/chain or stem 103"; wire 12'.

Lamps: Three medium base lamps, each 100w max.



P4489-20



P4489-20



P4489-09



P4489-09

MINI-PENDANT

P5270-09 Brushed Nickel

P5270-20 Antique Bronze

Chain- or stem-hung mini-pendant. Includes 6' of chain and two 6" stems.

Size: 6" dia., 7" ht. Overall ht. w/chain or stem 94"; wire 10'.

Lamp: One medium base lamp, 100w max.



P5270-20



P5270-09



FIVE-LIGHT CHANDELIER
P4490-09 Brushed Nickel
P4490-20 Antique Bronze
Chain- or stem-hung chandelier.
Includes 6' of chain and two
6" stems.
Size: 24" dia., 18-7/8" ht. Overall
ht. w/chain or stem 105"; wire 12'.
Lamps: Five medium base lamps,
each 100w max.



THREE-LIGHT FOYER

P3587-09 Brushed Nickel

P3587-20 Antique Bronze

Chain- or stem-hung foyer.

Includes 6' of chain and two 6" stems.

Size: 14-5/8" dia., 17" ht. Overall ht. w/chain or stem 104"; wire 12'.

Lamps: Three candelabra base lamps, each 60w max.





P4492-09



P4492-09

NINE-LIGHT CHANDELIER

P4492-09 Brushed Nickel

P4492-20 Antique Bronze

Two-tier. Chain- or stem-hung chandelier. Includes 6' of chain and two 6" stems.

Size: 28" dia., 27-3/4" ht. Overall ht. w/chain or stem 115"; wire 15'. Lamps: Nine medium base lamps, each 100w max.



P4492-20



P4492-20



Shown: P5707-09 Bay Court Lanterns.

Bay Court

Etched interior glass surrounded by etched water glass. For use indoor or outdoor. Damp location listed.

See pages 47 of Progress Catalog 129 for matching Bay Court fixtures.

ONE-LIGHT CLOSE-TO-CEILING

P3941-09 Brushed Nickel
P3941-20 Antique Bronze
Size: 11-5/8" dia., 11" ht.
Lamp: One medium base lamp, 100w max.



P3941-09



P3942-09



P3942-20

TWO-LIGHT CLOSE-TO-CEILING

P3942-09 Brushed Nickel
P3941-20 Antique Bronze
Size: 15" dia., 7-3/8" ht.
Lamps: Two medium base lamps, each 75w max.



P3941-20

Haven

Iron framework with stonehenge glass.



P5134-124EBWB

CFL MINI-PENDANT

P5134-124EBWB Copper Bronze
Includes one 6", four 12" stems and 6 links of chain.
Size: 7-1/2" sq., 11-3/4" ht. Overall ht. w/chain or stem 79"; wire 120".
Lamp: One 13w GU24 CFL lamp, included.





P2851-09 Semi flush and P4459-09 Chandelier in the Alexa Collection

Alexa

Soft, patterned etched glass
in Brushed Nickel finish.

See pages 37 of Progress
Catalog 129 for matching
Alexa fixtures.



NINE-LIGHT CHANDELIER

P4626-09 Brushed Nickel

Two-tier.

Size: 28" dia., 28-1/2" ht. Overall
ht. w/chain 102"; wire 15'.

Lamps: Nine medium base
lamps, each 60w max.



FOUR-LIGHT LINEAR CHANDELIER

P4619-09 Brushed Nickel

Size: 34" L., 4-1/2" W., 20" ht.

Overall ht. w/chain 93"; wire 15'.

Lamps: Four medium base
lamps, each 60w max.

Rave

Oval tubing frame is accented by sweeping straps and softly arching curves. Opal etched glass shades and candelabra sockets.

Available in -77 Forged Bronze and -09 Brushed Nickel finishes

All Rave hanging fixtures include one 6", four 12" stems and 6 links of chain.

THREE-LIGHT CHANDELIER

P4641-09 Brushed Nickel

P4641-77 Forged Bronze

Size: 20" dia., 17-3/8" ht. Overall ht. w/chain 80"; wire 180".

Lamps: Three G16-1/2 candelabra base lamps, each 60w max.



P5128-09WB Brushed Nickel

P5128-77WB Forged Bronze

Size: 7" dia., 10-3/4" ht. Overall ht. w/chain or stem 76"; wire 120".

Lamp: One candelabra base krypton lamp, 60w max. included





P3550-09



P3550-77

TWO-LIGHT SEMI-FLUSH

P3550-09 Brushed Nickel

P3550-77 Forged Bronze

Size: 13-1/4" dia., 9-1/2" ht.

Lamps: Two medium base lamps, each 100w max.



P4642-09



P4642-77

FIVE-LIGHT CHANDELIER

P4642-09 Brushed Nickel

P4642-77 Forged Bronze

Size: 24-1/2" dia., 20-3/4" ht.

Overall ht. w/chain 84";

wire 180".

Lamps: Five G16-1/2 candelabra base lamps, each 60w max.

P3944-77

**THREE-LIGHT INVERTED
PENDANT**

P3944-09 Brushed Nickel
P3944-77 Forged Bronze
Size: 19" dia., 23-1/2" ht. Overall
ht. w/chain 89"; wire 180".
Lamps: Three medium base
lamps, each 100w max.

P3944-09



P3945-09



P3945-77



TWO-LIGHT FOYER
P3945-09 Brushed Nickel
P3945-77 Forged Bronze
Size: 12" dia., 32-1/2" ht. Overall
ht. w/chain 95"; wire 180".
Lamps: Two medium base lamps,
each 100w max.



P4643-09



P4643-77

NINE-LIGHT CHANDELIER

P4643-09 Brushed Nickel

P4643-77 Forged Bronze

Two-tier.

Size: 27" dia., 27-1/4" ht. Overall
ht. w/chain 87"; wire 180".

Lamps: Nine G16-1/2 candelabra
base lamps, each 60w max.



Bravo

A current, truly transitional style is achieved with Bravo's free-flowing arms that are gracefully suspended with fluted shaped glass shades.

Bravo is available in an Antique Bronze finish with etched amber linen shades or white etched glass shades with a Brushed Nickel finish.



P4621-20



P4621-09

THREE-LIGHT CHANDELIER

P4621-09 Brushed Nickel

P4621-20 Antique Bronze

Size: 23" dia., 20-1/8" ht. Overall ht. w/chain 95"; wire 12'.

Lamps: Three medium base lamps, each 100w max.



P4622-09



P4622-20

FOUR-LIGHT CHANDELIER

P4622-09 Brushed Nickel

P4622-20 Antique Bronze

Size: 24" dia., 21" ht. Overall ht. w/chain 96"; wire 12'.

Lamps: Four medium base lamps, each 100w max.

FAN LIGHT KIT

P2650-09 Brushed Nickel
P2650-20T Antique Bronze
 Universal-style light kit with quick-connect wiring.
 Size: 11" dia., 5-1/2" ht.
 Lamps: Three candelabra base lamps, each 40w max. included



P2650-09



P2650-20T

P3821-20



P3821-09



THREE-LIGHT FOYER
P3821-09 Brushed Nickel
P3821-20 Antique Bronze
 Size: 18" dia., 21-1/2" ht. Overall
 ht. w/chain 96"; wire 12'.
 Lamps: Three candelabra base
 lamps, each 60w max.

P3912-09



P3912-20



THREE-LIGHT FOYER
P3912-09 Brushed Nickel
P3912-20 Antique Bronze
 Size: 21" dia., 23-1/2" ht.
 Overall ht. w/chain 98";
 wire 12'.
 Lamps: Three medium base
 lamps, each 100w max.



P4623-09



P4623-20

FIVE-LIGHT CHANDELIER
P4623-09 Brushed Nickel
P4623-20 Antique Bronze
 Size: 27" dia., 23" ht. Overall ht. w/chain 97"; wire 12'.
 Lamps: Five medium base lamps, each 100w max.



P4625-09

NINE-LIGHT CHANDELIER
P4625-09 Brushed Nickel
P4625-20 Antique Bronze
 Two-tier.
 Size: 32" dia., 31" ht. Overall ht. w/chain 106"; wire 12'.
 Lamps: Nine medium base lamps, each 100w max.



P5300-09



P5300-20

MINI-PENDANT
P5300-09 Brushed Nickel
P5300-20 Antique Bronze
 Chain- or stem-hung mini-pendant. Includes 6' of chain and two 6" stems.
 Size: 7-1/4" dia., 6-1/2" ht. Overall ht. w/chain or stem 94"; wire 10'.
 Lamp: One medium base lamp, 100w max.

Gather

Simplified frame with updated styling and elegant etched glass shades.

Available in -09 Brushed Nickel, -20 Antique Bronze and -31 Black finishes



P4440-09
P4440-09EBWB



P4440-20
P4440-20EBWB

THREE-LIGHT CHANDELIER
P4440-09 Brushed Nickel
P4440-20 Antique Bronze
Size: 18 1/2" dia., 15" ht. Overall
ht. w/chain 60"; wire 96".
Lamps: Three medium base
lamps, each 100w max.

THREE-LIGHT CFL CHANDELIER
P4440-09EBWB Brushed Nickel
P4440-20EBWB Antique Bronze
Size: 18-1/2" dia., 15" ht. Overall
ht. w/chain 60"; wire 96".
Lamps: Three 13w GU24 CFL
lamps, included.



P4441-09
P4441-09EBWB



P4441-20
P4441-20EBWB

FIVE-LIGHT CHANDELIER
P4441-09 Brushed Nickel
P4441-20 Antique Bronze
Size: 20-1/2" dia., 15" ht.
Overall ht. w/chain 60";
wire 96".
Lamps: Five medium base
lamps, each 100w max.

FIVE-LIGHT CFL CHANDELIER
P4441-09EBWB Brushed Nickel
P4441-20EBWB Antique Bronze
Size: 20-1/2" dia., 15" ht. Overall
ht. w/chain 60"; wire 96".
Lamps: Five 13w GU24 CFL
lamps, included.



TWO-LIGHT INVERTED PENDANT

P3914-09 Brushed Nickel

P3914-20 Antique Bronze

Size: 15" dia., 20-5/8" ht.

Overall ht. w/chain 66";

wire 96".

Lamps: Two medium base lamps, each 100w max.

TWO-LIGHT INVERTED CFL PENDANT

P3914-09EBWB Brushed Nickel

P3914-20EBWB Antique Bronze

Size: 15" dia., 20-5/8" ht. Overall

ht. w/chain 66"; wire 96".

Lamps: Two 13w GU24 CFL lamps, included.



NINE-LIGHT CHANDELIER

P4627-09 Brushed Nickel

P4627-20 Antique Bronze

Two-tier.

Size: 27-3/4" dia., 20-1/2" ht.

Overall ht. w/chain 84";

wire 120".

Lamps: Nine medium base lamps, each 100w max.



NINE-LIGHT CFL CHANDELIER

P4627-09EBWB Brushed Nickel

P4627-20EBWB Antique Bronze

Two-tier.

Size: 27-3/4" dia., 20-1/2" ht. Overall

ht. w/chain 84"; wire 120".

Lamps: Nine 13w GU24 CFL lamps, included.





P3928-09



P3928-20

THREE-LIGHT FOYER

P3928-09 Brushed Nickel

P3928-20 Antique Bronze

Size: 10" dia., 16" ht. Overall ht. w/chain 61"; wire 96".

Lamps: Three candelabra base lamps, each 60w max.



P3929-09



P3929-20

SIX-LIGHT FOYER

P3929-09 Brushed Nickel

P3929-20 Antique Bronze

Size: 15" dia., 24" ht. Overall ht. w/chain 87"; wire 120".

Lamps: Six candelabra base lamps, each 60w max.



P5113-09

P5113-09EBWB

P5113-20

P5113-20EBWB

MINI-PENDANT

P5113-09 Brushed Nickel

P5113-20 Antique Bronze

Chain- or stem-hung mini-pendant. Includes 42" of chain and two 6" stems.

Size: 4" dia., 5-3/4" ht. Overall ht. w/chain/stem 63"; wire 96".

Lamp: One medium base lamp, 100w max.

CFL MINI-PENDANT

P5113-09EBWB Brushed Nickel

P5113-20EBWB Antique Bronze

Chain- or stem-hung mini-pendant.

Includes 42" of chain and two 6" stems.

Size: 4" dia., 5-3/4" ht. Overall ht. w/chain/stem 63"; wire 96".

Lamp: One 13w GU24 CFL lamp, included.



Heart

Inspired by love. Iron arms mimic the shape of a heart. Candelabra version or etched glass shades share the same frame. Curvaceous, flowing and competitively priced.

Available in -09 Brushed Nickel and -20 Antique Bronze finishes



THREE-LIGHT CHANDELIER

P4664-09 Brushed Nickel

P4664-20 Antique Bronze

Size: 22" dia., 18" ht. Overall ht. w/chain 63"; wire 96".

Lamps: Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4666-09 Brushed Nickel

P4666-20 Antique Bronze

Size: 25-1/2" dia., 19-1/8" ht.

Overall ht. w/chain 63"; wire 96".

Lamps: Five medium base lamps, each 100w max.



Heart



P4665-09



P4665-20

THREE-LIGHT CHANDELIER

P4665-09 Brushed Nickel

P4665-20 Antique Bronze

Size: 20" dia., 18" ht. Overall ht. w/chain 63"; wire 96".

Lamps: Three candelabra base lamps, each 60w max.



P4667-09



P4667-20

FIVE-LIGHT CHANDELIER

P4667-09 Brushed Nickel

P4667-20 Antique Bronze

Size: 23-1/2" dia., 19-1/8" ht. Overall ht. w/chain 63"; wire 96".

Lamps: Five candelabra base lamps, each 60w max.

Heart

THREE-LIGHT INVERTED PENDANT

P3955-09 Brushed Nickel

P3955-20 Antique Bronze

Size: 17-3/4" dia., 21-3/4" ht.

Overall ht. w/chain 66"; wire 96".

Lamps: Three medium base lamps, each 100w max.



NINE-LIGHT CHANDELIER

P4669-09 Brushed Nickel

P4669-20 Antique Bronze

Two-tier.

Size: 28" dia., 28" ht. Overall ht. w/chain 91"; wire 144".

Lamps: Nine candelabra base lamps, each 60w max.

Heart



MINI-PENDANT
P5131-09 Brushed Nickel
P5131-20 Antique Bronze
Chain- or stem-hung mini-pendant.
Includes 42" of chain and
two 6" stems.
Size: 6" dia., 6" ht. Overall ht. w/
chain or stem 63"; wire 96".
Lamp: One medium base lamp,
100w max.

NINE-LIGHT CHANDELIER
P4668-09 Brushed Nickel
P4668-20 Antique Bronze
Two-tier.
Size: 30" dia., 27-3/4" ht. Overall
ht. w/chain 90"; wire 144".
Lamps: Nine medium base
lamps, each 100w max.

Moments

An urban-inspired family. Elongated profile on etched white glass. Constructed frame features industrialized influences.

Available in -81 Antique Nickel finish.

All Moments hanging fixtures have one 6", four 12" stems and 6 links of chain.

THREE-LIGHT CHANDELIER

P4670-81 Antique Nickel
Size: 22" dia., 19-3/4" ht. Overall ht. w/stem 87"; wire 144".
Lamps: Three medium base lamps, each 100w max.

P4670-81



P3959-81



THREE-LIGHT INVERTED PENDANT

P3959-81 Antique Nickel
Size: 22" dia., 24-1/2" ht. Overall ht. w/stem 90"; wire 144".
Lamps: Three medium base lamps, each 100w max.

P4672-81



NINE-LIGHT CHANDELIER

P4672-81 Antique Nickel
Size: 32-3/4" dia., 31-1/2" ht. Overall ht. w/stem 97"; wire 180".
Lamps: Nine medium base lamps, each 100w max.

Moments

THREE-LIGHT SEMI-FLUSH

P3952-81 Antique Nickel
Size: 15-3/4" dia., 12-1/4" ht.
Lamps: Three medium base lamps, each 75w max.



TWO-LIGHT CLOSE-TO-CEILING

P3953-81 Antique Nickel
Size: 14-1/2" dia., 6" ht.
Lamps: Two medium base lamps, each 75w max.



SIX-LIGHT CHANDELIER

P4671-81 Antique Nickel
Size: 26" dia., 24" ht. Overall ht. w/stem 90"; wire 144".
Lamps: Six medium base lamps, each 100w max.



ONE-LIGHT SCONCE

P7048-81 Antique Nickel
Size: 4-1/2" W., 11-1/4" ht. Extends 6".
Lamp: One medium base lamp, 100w max.



MINI-PENDANT

P5006-81 Antique Nickel
Size: 4-1/2" dia., 9-1/4" ht. Overall ht. w/stem 76"; wire 120".
Lamp: One base lamp, w max.

Orbitz

Customization accommodates variety of lifestyle and lighting needs. Rectilinear tubing frames and ring feature cast accents. White etched glass shades.

-09 Six-light chandeliers can be mounted with glass up or down.

Available in -09 Brushed Nickel and -20 Antique Bronze finishes

All Orbitz stem hung fixtures feature one 6", four 12" stems and 6 links of chain unless otherwise noted.



SIX-LIGHT OVAL CHANDELIER
P4660-20 Antique Bronze
Includes two 6" stems and 72" chain.
Size: 32" L., 16-3/4" W., 12" ht.
Overall ht. w/chain 99"; wire 180".
Lamps: Six medium base lamps, each 100w max.



SIX-LIGHT OVAL CHANDELIER
P4662-09 Brushed Nickel
Can be mounted with glass up or down
Size: 34" L., 16-5/8" W., 13-1/4" ht.
Overall ht. w/stem 80"; wire 180".
Lamps: Six medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER
P4659-20 Antique Bronze
Size: 23-1/4" dia., 18-1/2" ht.
Overall ht. w/stem 83"; wire 180".
Lamps: Five medium base lamps, each 100w max.





NINE-LIGHT CHANDELIER
P4663-09 Brushed Nickel
P4463-20 Antique Bronze
Size: 27" dia., 23-3/4" ht. Overall
ht. w/stem 90"; wire 180".
Lamps: Nine medium base
lamps, each 100w max.



MINI-PENDANT
P5114-09 Brushed Nickel
P5114-20 Antique Bronze
Size: 4" dia., 7-3/4" ht. Overall ht.
w/chain or stem 73"; wire 120".
Lamp: One medium base lamp,
100w max.



THREE-LIGHT CONVERTIBLE

P3954-09 Brushed Nickel

P3954-20 Antique Bronze
Chain and ceiling mounts
both included.

Size: 17" dia., 12 1/4" ht. Overall
ht. w/stem 79"; wire 180".

Lamps: Three medium base
lamps, each 100w max.



P3954-09



P3954-20



P3954-09



P4661-09
*shown with glass
mounted down*



P4661-09
*shown with glass
mounted up*

SIX-LIGHT CHANDELIER

P4661-09 Brushed Nickel

Can be mounted with glass up
or down.

Size: 24" dia., 18-3/4" ht. Overall
ht. w/chain 84"; wire 180.

Lamps: Six medium base lamps,
each 100w max.

Caress

Cares features a chic, sophisticated frame with cylindrical glass shades. Etched glass diffuser inside clear waterglass. Small foyer fixture is convertible. Chandeliers come with 60W Krypton lamp.

Available in -104 Polished Nickel finish

All Caress hanging fixtures include one 6", four 12" stems and 6 links of chain.



P3682-104

THREE-LIGHT INVERTED PENDANT

P3682-104 Polished Nickel
Size: 22" dia., 25-3/4" ht. Overall ht. w/chain 91"; wire 180".
Lamps: Three medium base lamps, each 100w max.



P4645-104WB

FIVE-LIGHT CHANDELIER

P4645-104WB Polished Nickel
Size: 27" dia., 22" ht. Overall ht. w/chain 88"; wire 180".
Lamps: Five E12 base krypton lamps, each 60w max., included.



P3946-104

ONE-LIGHT FOYER

P3946-104 Polished Nickel
Size: 14" dia., 30" ht. Overall ht. w/chain 96"; wire 180".
Lamp: One medium base lamp, 100w max.





P7046-104WB

ONE-LIGHT WALL
SCONCE

P7046-104WB Polished Nickel
Size: 8" W., 15" ht. Extends
9-1/2". H/CTR 8-7/8".
Lamp: One E12 base krypton
lamp, 60w max. included.



P4644-104WB

THREE-LIGHT CHANDELIER

P4644-104WB Polished Nickel
Size: 22" dia., 24-1/2" ht. Overall
ht. w/chain 91"; wire 180".
Lamps: Three E12 base krypton
lamps, each 60w max., included.



P3947-104

ONE-LIGHT FOYER

P3947-104 Polished Nickel
Size: 18" dia., 44-3/4" ht.
Overall ht. w/chain 111";
wire 180".
Lamp: One medium base
lamp, 100w max.





P3434-104

TWO-LIGHT SEMI-FLUSH
P3434-104 Polished Nickel
Size: 16" dia., 12" ht.
Lamps: Two medium base
lamps, each 100w max.



P5044-104WB



P5044-104WB

MINI-PENDANT
P5044-104WB Polished Nickel
Chain- or stem-hung mini-pendant.
Size: 6-3/8" dia., 10-3/4" ht. Overall
ht w/chain or stem 77"; wire 180".
Lamp: One E12 base krypton
lamp, 60w max., included.

P4646-104WB



NINE-LIGHT CHANDELIER
P4646-104WB Polished Nickel
Two-tier.
Size: 36-5/8" dia., 33-5/8" ht.
Overall ht. w/chain 100";
wire 180".
Lamps: Nine E12 base krypton
lamps, each 60w max., included.

LadyLuck

Sophisticated, elongated profiles. Handspun cups feature feminine styling. Tall, elegant mouth-blown opal etched glass shades and flowing rectangular arms create a soft, classic frame.

Available in -104 Polished Nickel finish.



THREE-LIGHT FOYER
P3960-104 Polished Nickel
Size: 18" dia., 26" ht. Overall ht. w/chain 101"; wire 96".
Lamps: Three candelabra base lamps, each 60w max.



FIVE-LIGHT CHANDELIER
P4677-104 Polished Nickel
Size: 25-3/4" dia., 25 1/4" ht.
Overall ht. w/chain 101"; wire 180".
Lamps: Five candelabra base lamps, each 60w max.



ONE-LIGHT SCONCE
P7050-104 Polished Nickel
Size: 5" W., 17-5/8" ht.
Extends 6-1/4".
Lamp: One candelabra base lamp, 60w max.



P4676-104

THREE-LIGHT CHANDELIER

P4676-104 Polished Nickel
Size: 18-1/2" dia., 17-3/4" ht.
Overall ht. w/chain 93";
wire 180".
Lamps: Three candelabra base
lamps, each 60w max.



P5008-104

MINI-PENDANT

P5008-104 Polished Nickel
Chain- or stem-hung mini-
pendant. Includes 6' of chain
and two 6" stems.
Size: 5-3/8" dia., 19-1/4" ht.
Overall ht. w/chain or stem 95";
wire 180".
Lamp: One candelabra base
lamp, 60w max.



P4678-104

NINE-LIGHT CHANDELIER

P4678-104 Polished Nickel
Two-tier.
Size: 35" dia., 33" ht. Overall ht.
w/chain 108"; wire 180".
Lamps: Nine candelabra base
lamps, each 60w max.

Fortune

Good fortune is your destiny, as seen in the teller's mystical crystal ball.

K9 glass orb accents and etched opal drum shades.

Available in -104 Polished Nickel finish.

THREE-LIGHT CHANDELIER
P4673-104 Polished Nickel
Size: 20" dia., 12-1/2" ht. Overall ht. w/chain 79"; wire 180".
Lamps: Three candelabra base G16-1/2 lamps, each 60w max.



MINI-PENDANT
P5007-104 Polished Nickel
Chain- or stem-hung mini-pendant. Includes 6' of chain and two 6" stems.
Size: 8-7/8" dia., 9-3/4" ht. Overall ht. w/chain or stem 76"; wire 120".
Lamp: One candelabra base G16-1/2 lamp, 60w max.



THREE-LIGHT PENDANT
P5034-104 Polished Nickel
Size: 20-1/4" dia., 15-5/8" ht. Overall ht. w/chain 82"; wire 180".
Lamps: Three medium base lamps, each 100w max.



Fortune



FIVE-LIGHT CHANDELIER
P4674-104 Polished Nickel
Size: 26" dia., 16-1/2" ht. Overall
ht. w/chain 83"; wire 180"
Lamps: Five candelabra base
lamps, each 60w max.



ONE-LIGHT SCONCE
P7049-104WB Polished Nickel
Size: 5-7/8" W., 8-3/4" ht.
Extends 7-3/4".
Lamp: One kryton base lamp,
60w max. included.



NINE-LIGHT CHANDELIER
P4675-104 Polished Nickel
Size: 31" dia., 15-3/8" ht. Overall
ht. w/chain 82"; wire 180".
Lamps: Nine candelabra base
G16-1/2 lamps, each 60w max.



Inspire

Updated traditional with gracious flowing oval arms. Back to basics design styling. Off-white linen drum shades.

Available in -09 Brushed Nickel and -20 Antique Bronze finishes



NINE-LIGHT CHANDELIER

P4638-09 Brushed Nickel

P4638-20 Antique Bronze

Two-tier.

Size: 29-3/8" dia., 31" ht.

Overall ht. w/chain 105";

wire 144".

Lamps: Nine candelabra base lamps, each 60w max.



P7026-30

CFL SCONCE

P7026-30 White

Size: 6" W., 9" ht.

Extends 3-7/8".

H/CTR 4-1/2".

Lamp: One 13w GU24 CFL lamp.



P8926-01

P8926-01

White Linen fabric shade

Size: 5-1/2" dia., 4-3/4" ht.



THREE-LIGHT CHANDELIER

P4632-09 Brushed Nickel

P4632-20 Antique Bronze

Size: 17" dia., 18" ht. Overall ht. w/chain 92-1/4"; wire 120".

Lamps: Three candelabra base lamps, each 60w max.



FIVE-LIGHT CHANDELIER

P4635-09 Brushed Nickel

P4635-20 Antique Bronze

Size: 23" dia., 20" ht. Overall ht. w/chain 94"; wire 120".

Lamps: Five candelabra base lamps, each 60w max.



P5065-20



P5065-09

MINI-PENDANT

P5065-09 Brushed Nickel

P5065-20 Antique Bronze

Chain- or stem-hung mini-pendant. Includes 6' of chain and two 6" stems.

Size: 6-1/2" dia., 6-1/4" ht.

Overall ht. w/chain or stem 93"; wire 120".

Lamp: One medium base lamp, 100w max.



P3939-20

P3939-09

CFL SEMI-FLUSH

P3939-09 Brushed Nickel

P3939-20 Antique Bronze

White acrylic diffuser.

Size: 13" dia., 10-3/8" ht.

Lamps: Two 26w GU24

CFL lamps.



P3931-09



P3931-20

THREE-LIGHT INVERTED PENDANT

P3931-09 Brushed Nickel

P3931-20 Antique Bronze

White acrylic diffuser.

Size: 19" dia., 21-1/2" ht. Overall ht. w/chain 96"; wire 120".

Lamps: Three medium base lamps, each 100w max.

Close-to-ceiling

Topaz glass



P3408-20T

ONE-LIGHT CLOSE-TO-CEILING

P3408-20T Antique Bronze
Size: 7-1/2" dia., 4-7/8" ht.
Lamp: One medium base lamp, 60w max.



P3410-20T

TWO-LIGHT CLOSE-TO-CEILING

P3410-20T Antique Bronze
Size: 9-1/2" dia., 5-1/4" ht.
Lamps: Two medium base lamps, each 60w max.



P3412-20T

TWO-LIGHT CLOSE-TO-CEILING

P3412-20T Antique Bronze
Size: 11-3/4" dia., 6" ht.
Lamps: Two medium base lamps, each 75w max.

Sconces



P7081-09

P7081-09 Brushed Nickel
Size: 4-1/2" W., 13-1/2" ht.
Extends 4". H/CTR 9-1/2".
Lamp: One GU24 base CFL lamp, 26w max.
ADA



P7081-09W



P7081-20W

P7153-09W Brushed Nickel with white opal glass
P7153-20T Antique Bronze with topaz glass
P7153-20W Antique Bronze with white opal glass
Size: 15 3/8" W., 7" ht. Extends 7 1/2". H/CTR 2-1/2".
Lamp: One medium base lamp, 60w max.



P7081-20T

Etched opal glass with clear glass disks.



P2012-104



P2013-104



P2014-104



P2015-104

Product No.	Finish	Description	Size	Lamp(s)
P2012-104	Polished Nickel	One-light	5-1/4" W., 9" ht. H/CTR 6-5/8". Extends 5-1/4".	1 medium base, 100w max
P2013-104	Polished Nickel	Two-light	14-5/8" W., 9" ht. H/CTR 6-5/8". Extends 5-1/4".	2 medium base, each 100w max.
P2014-104	Polished Nickel	Three-light	24" W., 9" ht. H/CTR 6-5/8". Extends 5-1/4".	3 medium base, each 100w max.
P2015-104	Polished Nickel	Four-light	33-1/2" W., 9" ht. H/CTR 6-5/8". Extends 5-1/4".	4 medium base, each 100w max.

Damp location listed.

Calven Bath

Etched opal glass



P3210-09WB



P3209-09WB



P3223-09WB



P3236-09WB

Product No.	Finish	Description	Size	Lamp(s)
P3209-09WB	Brushed Nickel	One-light	6-3/8" W., 11" ht. H/CTR 6". Extends 7-5/8".	1 halogen G9 base, 60w max
P3210-09WB	Brushed Nickel	Two-light	18" W., 6" ht. H/CTR 3". Extends 7-7/8".	2 halogen G9 base, each 60w max.
P3223-09WB	Brushed Nickel	Three-light	25" W., 6" ht. H/CTR 3". Extends 7-7/8".	3 halogen G9 base, each 60w max.
P3236-09WB	Brushed Nickel	Four-light	34-3/8" W. 6-1/2" ht. H/CTR 3". Extends 7-7/8".	4 halogen G9 base, each 60w max.

Damp location listed.

All fixtures on these pages mount up or down.

Joy Bath



P2000-20



P2002-20



P2001-20



P2003-20



P2000-09



P2002-09



P2001-09



P2003-09

Product No.	Finish	Description	Size	Lamp(s)
P2000-09	Brushed Nickel	One-light	6" W., 9-1/2" ht.	1 medium base, 100w max.
P2000-20	Antique Bronze		H/CTR 6". Extends 7".	
P2001-09	Brushed Nickel	Two-light	14" W., 7-5/8" ht.	2 medium base, each 100w max.
P2001-20	Antique Bronze		H/CTR 4-1/8". Extends 8-1/8".	
P2002-09	Brushed Nickel	Three-light	22" W., 7-5/8" ht.	3 medium base, each 100w max.
P2002-20	Antique Bronze		H/CTR 4-1/8". Extends 8-1/8".	
P2003-09	Brushed Nickel	Four-light	30" W., 7-5/8" ht.	4 medium base, each 100w max.
P2003-20	Antique Bronze		H/CTR 4-1/8". Extends 8-1/8".	

All fixtures on these pages mount up or down.

Bravo Bath



Product No.	Finish	Description	Size	Lamp(s)
P2004-09	Brushed Nickel	One-light	7-1/4" W., 9" ht.	1 medium base,
P2004-20	Antique Bronze		H/CTR 4-1/2".	100w max.
			Extends 8-3/4".	
P2005-09	Brushed Nickel	Two-light	17" W., 8-1/2" ht.	2 medium base,
P2005-20	Antique Bronze		H/CTR 6-1/8".	each 100w max.
			Extends 8-3/4".	
P2006-09	Brushed Nickel	Three-light	26-3/4" W., 8-3/4" ht.	3 medium base,
P2006-20	Antique Bronze		H/CTR 6-3/8".	each 100w max.
			Extends 8-3/4".	
P2007-09	Brushed Nickel	Four-light	37-1/4" W., 9" ht.	4 medium base,
P2007-20	Antique Bronze		H/CTR 6-1/2".	each 100w max.
			Extends 8-3/4".	



Gather Bath



P2707-09
P2707-09EBWB



P2709-09
P2709-09EBWB



P2706-09
P2706-09EBWB



P2713-09



P2706-20
P2706-20EBWB



P2708-20
P2708-20EBWB







P2707-20
P2707-20EBWB



P2713-20

Product No.	Finish	Description	Size	Lamp(s)
P2706-09	Brushed Nickel	One-light	5" W., 7-1/2" ht.	1 medium base,
P2706-20	Antique Bronze		H/CTR 2-5/8".	100w max.
			Extends 6-1/2".	
P2707-09	Brushed Nickel	Two-light	12" W., 7-1/2" ht.	2 medium base,
P2707-20	Antique Bronze		H/CTR 2-1/2".	each 100w max.
			Extends 6-1/2".	
P2708-09	Brushed Nickel	Three-light	24" W., 7-1/2" ht.	3 medium base,
P2708-20	Antique Bronze		H/CTR 2-1/2".	each 100w max.
			Extends 6-1/2".	
P2709-09	Brushed Nickel	Four-light	30" W., 7-1/2" ht.	4 medium base,
P2709-20	Antique Bronze		H/CTR 2-1/2".	each 100w max.
			Extends 6-1/2".	
P2713-09	Brushed Nickel	Five-light	36" W., 7-1/2" ht.	5 medium base,
P2713-20	Antique Bronze		H/CTR 2-1/2".	each 100w max.
			Extends 6-1/2".	
P2714-09	Brushed Nickel	Six-light	48" W., 7-1/2" ht.	6 medium base,
P2714-20	Antique Bronze		H/CTR 2-1/2".	each 100w max.
			Extends 6-1/2".	

Damp location listed.

Product No.	Finish	Description	Size	Lamp(s)
P2706-09EBWB	Brushed Nickel	One-light	5" W., 7-1/2" ht.	1 13w GU24 CFL
P2706-20EBWB	Antique Bronze		H/CTR 2-5/8".	included
			Extends 6-1/2".	
P2707-09EBWB	Brushed Nickel	Two-light	12" W., 7-1/2" ht.	2 13w GU24 CFL
P2707-20EBWB	Antique Bronze		H/CTR 2-1/2".	included
			Extends 6-1/2".	
P2708-09EBWB	Brushed Nickel	Three-light	24" W., 7-1/2" ht.	3 13w GU24 CFL,
P2708-20EBWB	Antique Bronze		H/CTR 2-1/2".	included
			Extends 6-1/2".	
P2709-09EBWB	Brushed Nickel	Four-light	30" W., 7-1/2" ht.	4 13w GU24 CFL
P2709-20EBWB	Antique Bronze		H/CTR 2-1/2".	included
			Extends 6-1/2".	

Damp location listed.

Gather Bath



P2714-09



P2714-20

Alexa Bath

Etched linen and clear glass

FOUR-LIGHT BATH

P2998-09 Brushed Nickel

Size: 31" W., 9-1/2" ht.

Extends 4-1/2".

Lamps: Four medium base lamps,
each 100w max.

Damp location listed.



P2998-09

See pages 333 of Progress Catalog
129 for additional Alexa fixtures.

All fixtures on these pages mount
up or down.

progresslighting.com

Adorn Bath

Created to easily coordinate with the Janos, Joy and Bravo families, Adorn features fluted glass shades that mount up or down on a curving frame.

Offered in a Brushed Nickel finish with etched glass or an Antique Bronze finish with etched light amber glass.



P2010-09



P2008-09



P2011-09



P2009-09



P2009-20



P2008-20



P2011-20



P2010-20

Product No.	Finish	Description	Size	Lamp(s)
P2008-09	Brushed Nickel	One-light	5-1/4" W., 6-3/4" ht.	1 medium base ,
P2008-20	Antique Bronze		H/CTR 3-3/8".	100w max.
			Extends 7".	
P2009-09	Brushed Nickel	Two-light	13-1/4" W., 6-5/8" ht.	2 medium base,
P2009-20	Antique Bronze		H/CTR 4-3/8".	each 100w max.
			Extends 6-1/4".	
P2010-09	Brushed Nickel	Three-light	21-1/2" W., 6-5/8" ht.	3 medium base,
P2010-20	Antique Bronze		H/CTR 4-3/8".	each 100w max.
			Extends 7-1/2".	
P2011-09	Brushed Nickel	Four-light	28-1/4" W., 6-5/8" ht.	4 medium base,
P2011-20	Antique Bronze		H/CTR 4-3/8".	each 100w max.
			Extends 7-1/2".	

Addison Bath

Delicate scalloped glass shades with etched glass finish. Coordinates with Delta's® Addison faucet collection in Champagne Bronze finish.



P2846-109



P2847-109



P2848-109




P3870-109

Product No.	Finish	Description	Size	Lamp(s)
P2846-109	Brushed Bronze	One-light	5-3/8" W., 9" ht. H/CTR 6-1/4". Extends 6-1/2".	1 medium base, 100w max
P2847-109	Brushed Bronze	Two-light	15-7/8" W., 9" ht. H/CTR 6-1/2". Extends 6-1/2".	2 medium base, each 100w max.
P2848-109	Brushed Bronze	Three-light	26" W., 9" ht. H/CTR 6-1/2". Extends 6-3/8".	3 medium base, each 100w max.

TWO-LIGHT CLOSE-TO-CEILING
P3870-109 Brushed Bronze
 Size: 12-5/8" dia., 6" ht.
 Lamps: Two medium base lamps, each 100w max.

Inspire Bath



Product No.	Finish	Description	Size	Lamp(s)
P2018-09	Brushed Nickel	One-light	4-5/8" W., 7-1/2" ht.	1 medium base, 100w max.
P2018-20	Antique Bronze		H/CTR 3-3/4". Extends 7-3/8".	
P2019-09	Brushed Nickel	Two-light	15" W., 8-1/2" ht.	2 medium base, each 100w max.
P2019-20	Antique Bronze		H/CTR 6-1/8". Extends 6-7/8".	
P2020-09	Brushed Nickel	Three-light	22-3/8" W., 8-1/4" ht.	3 medium base, each 100w max.
P2020-20	Antique Bronze		H/CTR 5-1/2". Extends 6-7/8".	
P2021-09	Brushed Nickel	Four-light	31-3/8" W., 8-1/2" ht.	4 medium base, each 100w max.
P2021-20	Antique Bronze		H/CTR 6-1/8". Extends 6-7/8".	

Damp location listed.



Fortune Bath

Opal glass shades



P7049-104WB

ONE-LIGHT BATH
P7049-104WB Polished Nickel
 Size: 5-7/8" W., 8-3/4" ht.
 Extends 7-3/4".
 Lamp: One kryton base lamp,
 60w max. included.



P2927-104EBWB

THREE-LIGHT BATH
P2927-104WB Polished Nickel
 Size: W., ht. Extends 7-3/4".
 Lamps: Three kryton base lamps,
 each 60w max. included.

Orbitz Bath

White glass shades.

See page 359 of catalog 129 for
 Brushed Nickel version.



P3057-20



P3030-20



P3058-20

Product No.	Finish	Description	Size	Lamp(s)
P3030-20	Antique Bronze	One-light	5-1/2" W., 7-1/4" ht. H/CTR 5". Extends 6".	1 medium base, 100w max.
P3057-20	Antique Bronze	Two-light	13" W., 7-1/4" ht. H/CTR 5". Extends 6-1/4".	2 medium base, each 100w max.
P3058-20	Antique Bronze	Three-light	21-3/4" W., 7-1/2" ht. H/CTR 5". Extends 8-1/4".	3 medium base, each 100w max.

Damp location listed.

All fixtures on these pages mount up or
 down.
progresslighting.com

Fan Light Kits




P2612-20T

P2612-20T Antique Bronze with etched light amber glass
P2612-20 Antique Bronze
 Universal-style light kit with quick-connect wiring.
 Etched light amber glass
 Size: 10-3/4" dia., 5-1/2" ht.
 Lamps: Three candelabra base lamps, each 40w max. included



P2612-20



P2643-20T

P2643-20T Antique Bronze with etched light amber glass
 Universal-style light kit with quick-connect wiring.
 Size: 13-5/8" dia., 7-3/4" ht.
 Lamps: Four candelabra base lamps, each 40w max. included



P2646-09



P2646-30



P2646-20

P2646-09 Brushed Nickel
P2646-20 Antique Bronze
P2646-30 White
 Universal-style light kit with quick-connect wiring. Adjustable metal shade with black baffle.
 Size: 9" dia. (adjustable to 11" dia.), 6-5/8" ht.
 Lamps: Three medium base CFL lamps included, each 13w max.
 Non-dimmable.

Bravo



P2650-09



P2650-20T

P2650-09 Brushed Nickel w/ etched glass
P2650-20T Antique Bronze w/etched light amber glass
 Universal-style light kit with quick-connect wiring.
 Size: 11" dia., 5-1/2" ht.
 Lamps: Three candelabra base lamps, each 40w max. included
 *Also coordinates w/ Joy Collection

Hoop

Energy efficient EBWB fixtures with simplistic styling. A cylindrical hoop encircles the opal etched glass diffuser.

Low profile, can be mounted on wall or ceiling.

Wet location listed.



P5781-20EBWB
shown ceiling-mounted

P5781-20EBWB Antique Bronze
Size: 10-1/2" dia., 4-7/8" ht.
Lamp: One GU24 base squat CFL lamp, 18w max. included



P5781-20EBWB
shown wall-mounted



P5786-20EBWB
shown ceiling-mounted



P5786-20EBWB
shown wall-mounted

P5786-20EBWB Antique Bronze
Size: 13-5/8" dia., 5-3/8" ht.
Lamp: One GU24 base squat CFL lamp, 26w max. included.



Peek-a-Boo

Etched glass shade "peeks through" arched frame. Clean, contemporary wall lanterns.

Small and large versions.

Available in -20 Antique Bronze finish.



P6602-20

P6602-20 Antique Bronze
Size: 5-1/2" W., 13" ht.
Extends 3-1/4". H/CTR 7-1/4".
Lamp: One candelabra base lamp, 60w max.



P6603-20

P6603-20 Antique Bronze
Size: 5-1/2" W., 17-1/8" ht.
Extends 3-1/4". H/CTR 10-3/4".
Lamp: One medium base T10 lamp, 60w max.

Coupe

Looped rectangular tubing frame.
Energy efficient fixture with etched
glass diffuser on inside.

-09 Brushed Nickel finish with
clear ribbed bent glass shade.

-74 Venetian Bronze finish with
clear, heavy-seeded outside bent
glass shade.

P6604-09EE Brushed Nickel
P6604-74EE Venetian Bronze
Size: 8" W., 14" ht. Extends 6".
H/CTR 7".
Lamp: One GU24 base CFL
lamp, 18w max.



P6605-09EE

P6605-09EE Brushed Nickel
P6605-74EE Venetian Bronze
Size: 9" W., 18" ht. Extends 9".
H/CTR 9".
Lamp: One GU24 base CFL lamp,
32w max.



P6604-09EE



P6604-74EE



P6605-74EE



Greetings

Greet guests with an architectural inspired frame. Modern drum profile and etched glass shades.

Available in -20 Antique Bronze finish.



P5631-20

P5631-20 Antique Bronze
Size: 5-3/4" W., 12-1/2" ht.
Extends 8". H/CTR 6-1/2".
Lamp: One medium base lamp,
100w max.



P5719-20

P5719-20 Antique Bronze
Size: 7-1/2" W., 16-3/4" ht.
Extends 10". H/CTR 9-1/8".
Lamp: One medium base lamp,
100w max.



P5449-20

P5449-20 Antique Bronze
Size: 9-1/2" dia., 23" ht. Fits 3"
post (order separately).
Lamp: One medium base
lamp, 100w max.



P5549-20

P5549-20 Antique Bronze
Size: 9-1/2" dia., 22-3/4" ht. Overall
ht w/chain 96"; wire 10'.
Lamp: One medium base lamp,
100w max.



P5728-20

P5728-20 Antique Bronze
Size: 9 1/2" W., 20-3/4" ht.
Extends 12-3/8". H/CTR 11-1/8".
Lamp: One medium base lamp,
100w max.

Bay Court

Rediscover antique Nautical
Lanterns with etched glass
surrounded by water glass.

Available in Brushed Nickel or
Antique Bronze.



P5589-09



P5589-20

P5589-09 Brushed Nickel
P5589-20 Antique Bronze
Size: 8-3/4" dia., 12-3/4" ht. Overall
ht w/chain 87"; wire 10'.
Lamp: One medium base lamp,
100w max.



P5849-09



P5849-20

P5849-09 Brushed Nickel
P5849-20 Antique Bronze
Size: 8-3/4" W., 10-1/4" ht.
Extends 10-3/8". H/CTR 5-1/4".
Lamp: One medium base lamp,
100w max.



Bay Court

ONE-LIGHT CLOSE-TO-CEILING

P3941-09 Brushed Nickel
P3941-20 Antique Bronze
 Size: 11-5/8" dia., 11" ht.
 Lamp: One medium base lamp,
 100w max.



P3942-09



P3942-20

TWO-LIGHT CLOSE-TO-CEILING

P3942-09 Brushed Nickel
P3941-20 Antique Bronze
 Size: 15" dia., 7-3/8" ht.
 Lamps: Two medium base
 lamps, each 75w max.



P3941-09



P3941-20

P5851-09 Antique Bronze
P5851-20 Antique Bronze
 Size: 11-5/8" W., 13-5/8" ht.
 Extends 13-3/8". H/CTR 7".
 Lamp: One medium base lamp,
 100w max.



P5851-09



P5851-20



P5499-09



P5499-20

P5499-09 Brushed Nickel
P5499-20 Antique Bronze
 Size: 8-3/4" dia., 14-1/2" ht.
 Fits 3" post (order separately).
 Lamp: One medium base
 lamp, 100w max.

Welcome

A classic lantern with modern styling. Etched opal glass features horizontal band. Opportunity to complement variety of architectural styles.

Available in -20 Antique Bronze finish.



P6003-20

P6003-20 Antique Bronze
Size: 7" W., 8-1/8" ht. Extends 7-3/4". H/CTR 3-1/4".
Lamp: One medium base lamp, 100w max.



P6004-20

P6004-20 Antique Bronze
Size: 9" W., 11" ht. Extends 9-7/8". H/CTR 4-3/4".
Lamp: One medium base lamp, 100w max.



P6506-20

P6506-20 Antique Bronze
Size: 9" dia., 12-7/8" ht. Overall ht. w/chain 78"; wire 180".
Lamp: One medium base lamp, 100w max.



P6406-20

P6406-20 Antique Bronze
Size: 9" dia., 14" ht. Fits 3" post (order separately).
Lamp: One medium base lamp, 100w max.



P6005-20

P6005-20 Antique Bronze
Size: 11" W., 13-1/2" ht. Extends 11-7/8". H/CTR 5-1/8".
Lamp: One medium base lamp, 100w max.

Regatta

Updated coastal styling meets contemporary design. Exterior clear seeded glass with etched opal glass inside.

Available in -20 Antique Bronze finish.



P5997-20

P5997-20 Antique Bronze
Size: 7-1/2" W., 11" ht.
Extends 7 3/4". H/CTR 6".
Lamp: One medium base lamp,
100Ww max.



P6505-20

P6505-20 Antique Bronze
Size: 9 1/2" dia., 15-1/2" ht. Overall
ht w/chain 87"; wire 120".
Lamp: One medium base lamp,
100Ww max.



P5998-20

P5998-20 Antique Bronze
Size: 9-1/2" W., 13" ht.
Extends 9-3/8". H/CTR 6-1/2".
Lamp: One medium base lamp,
100Ww max.



P6405-20

P6405-20 Antique Bronze
Size: 9-1/2" dia., 16-3/4" ht.
Fits 3" post (order separately).
Lamp: One medium base
lamp, 100Ww max.

Merit

Inset square etched glass shades within rectilinear frame. Cast aluminum construction. Frame showcases pierced grid pattern.

Durable powder coat finish.

Available in -31 Black painted finish.



P6000-31

P6000-31 Black
Size: 5-1/4" sq., 8" ht.
Extends 6-1/4".
H/CTR 2-1/2".
Lamp: One medium base lamp, 60w max.



P6001-31

P6001-31 Black
Size: 7-3/4" sq., 12-1/4" ht.
Extends 9". H/CTR 3".
Lamp: One medium base lamp, 100w max.



P6002-31

P6002-31 Black
Size: 10" sq., 15-3/4" ht.
Extends 11-3/8". H/CTR 4".
Lamp: One medium base lamp, 100w max.



P6500-31

P6500-31 Black
Size: 10" sq., 17-1/2" ht. Overall ht. w/chain 91"; wire 120".
Lamp: One medium base lamp, 100w max.



P6400-31

P6400-31 Black
Size: 10" sq., 18-3/4" ht. Fits 3" post (order separately).
Lamp: One medium base lamp, 100w max.

Mac

With essential back-to-basics design styling, Mac outdoor lanterns feature a classic Arts and Crafts-inspired profile that is ideal for many home exteriors, from lodge to bungalow. A durable textured Black powder coat finish, cast aluminum construction and clear water glass accentuates the simplified design.



P5906-31

P5906-31 Black
One-light wall lantern.
Size: 6" sq., 8-1/2" ht.
Extends 7-1/8".
Lamp: One medium base lamp, 100w max.



P5907-31

P5907-31 Black
One-light wall lantern.
Size: 8-3/4" sq., 12-1/4" ht.
Extends 10-1/8".
Lamp: One medium base lamp, 100w max.

Soul

Individual one-light wall sconce for indoor/outdoor use. Sculptural styling becomes a statement piece.

Etched glass and available in -20 Antique Bronze finish.

P5819-20EE Antique Bronze
Size: 12" W., 19-3/4" ht. Extends 6".
H/CTR 9-7/8".
Lamp: One GU24 base CFL lamp, 26w max.



P5819-20EE



Reside

Outdoor lanterns feature classic, traditional styling with clear ribbed glass.

Cast aluminum with durable powder coat finish

Available in -108 hand painted Oil Rubbed Bronze finish



P5977-108

P5977-108 Oil Rubbed Bronze
 Size: 6" W., 11-3/8" ht. Extends 7-1/8". H/CTR 4".
 Lamp: One medium base lamp, 100w max.



P5978-108

P5978-108 Oil Rubbed Bronze
 Size: 7-1/2" W., 14-1/4" ht. Extends 8 3/4". H/CTR 5".
 Lamp: One medium base lamp, 100w max.



P6502-108

P6502-108 Oil Rubbed Bronze
 Size: 7-1/2" dia., 15-1/2" ht. Overall ht w/chain 90"; wire 15'.
 Lamp: One medium base lamp, 100w max.



P6402-108

P6402-108 Oil Rubbed Bronze
 Size: 7-1/2" dia., 17-3/4" ht. Fits 3" post (order separately).
 Lamp: One medium base lamp, 100w max.



P5979-108

P5979-108 Oil Rubbed Bronze
 Size: 9-1/2" W., 18" ht. Extends 11". H/CTR 8".
 Lamp: One medium base lamp, 100w max.

Pedigree

Cast aluminum construction with durable powder coat finish. Cast pyramidal block and fluted uprights. Energy efficient outdoor lanterns with classic styling.

Etched seeded glass diffuser and GU24 socket.

Available in -97 Autumn Haze finish.

P6503-97 Autumn Haze
 Size: 9" dia., 13-5/8" ht. Overall ht w/chain 88; wire 15'.
 Lamp: One GU24 base CFL lamp, 26w max.



P6503-97



P5980-97

P5980-97 Autumn Haze
 Size: 7" W., 10" ht. Extends 8-1/2".
 H/CTR 2-3/4".
 Lamp: One GU24 base CFL lamp, 26w max.



P5982-97

P5982-97 Autumn Haze
 Size: 11-1/2" W., 16-1/2" ht.
 Extends 13-1/2". H/CTR 5-3/4".
 Lamp: One GU24 base lamp, 26w max.



P6403-97

P6403-97 Autumn Haze
 Size: 9" dia., 16-3/8" ht. Fits 3" post (order separately).
 Lamp: One GU24 base CFL lamp, 26w max.



P5981-97

P5981-97 Autumn Haze
 Size: 9" W., 13-3/8" ht.
 Extends 10-1/2".
 H/CTR 5-3/4".
 Lamp: One GU24 base CFL lamp, 26w max.



Resort

Tudor styling meets Prairie design. Gradual umber tint on glass shades. A woven cast pattern encases a casual profile.

Cast aluminum lanterns feature powder coat finish

Available in -122 Aged Copper finish with Pietra accents



P5987-122

P5987-122 Aged Copper
Size: 6-1/2" W., 10-7/8" ht.
Extends 7-1/2". H/CTR 3-1/2".
Lamp: One medium base lamp,
100w max.



P6504-122



P6504-122 Aged Copper
Decorative bottom grill
Size: 8-1/2" dia., 14-1/8" ht. Overall
ht. w/chain 88"; wire 15".
Lamp: One medium base lamp,
100w max.



P5988-122

P5988-122 Aged Copper
Size: 8-1/2" W., 15-7/8" ht.
Extends 11-1/4".
H/CTR 4-3/4".
Lamp: One medium base
lamp, 100w max.



P6404-20

P6404-122 Aged Copper
Decorative bottom grill
Size: 8-1/2" dia., 17-3/8" ht.
Fits 3" post (order separately).
Lamp: One medium base
lamp, 100w max.



P5989-122

P5989-122 Aged Copper
Size: 10-1/2" W., 19-3/4" ht.
Extends 14". H/CTR 5-7/8".
Lamp: One medium base
lamp, 100w max.

Imperial

Outdoor lanterns with simplistic styling. Etched drum shade floats around iron framework. Open and airy.

Traditional shape and profile with contemporary twist

Available in -20 Antique Bronze finish

Two 6", one 12", two 15" stems on hanging fixtures.

P6507-20 Antique Bronze
Includes one 6", four 12" stems and 6 links of chain.
Size: 14-3/4" dia., 20-1/2" ht.
Overall ht. w/stem 86"; wire 120".
Lamp: One medium base lamp, 100w max.



P6508-20 Antique Bronze
Stem hung lantern.
Size: 18-3/4" dia., 23-5/8" ht.
Overall ht. w/stem 91"; wire 120".
Lamp: One medium base lamp, 100w max.



P6600-20 Antique Bronze
Size: 12" dia., 17-1/8" ht. Extends 9-1/8". H/CTR 9".
Lamp: One medium base lamp, 100w max.

P6600-20

P6407-20 Antique Bronze
Size: 12" dia., 19-3/4" ht. Fits 3" post (order separately).
Lamp: One medium base lamp, 100w max.



P6407-20



P6601-20

P6601-20 Antique Bronze
Size: 14-3/4" dia., 20-1/2" ht.
Extends 11-3/8". H/CTR 10-1/2".
Lamp: One medium base lamp, 100w max.

Enchant

A gracious cast pattern. Clear seeded glass with cast aluminum frame. Delicate, decorative paisley scrolled details and available in -84 Espresso painted finish.



P5966-84

P5966-84 Espresso
 Size: 9-1/2" sq., 19-1/4" ht.
 Extends 12-1/4".
 H/CTR 8-3/4".
 Lamp: One medium base lamp, 100w max.



P5959-84

P5959-84 Espresso
 Size: 7-1/2" sq., 15-1/8" ht.
 Extends 9-5/8". H/CTR 5-3/4".
 Lamp: One medium base lamp, 100w max.



P5967-84

P5967-84 Espresso
 Size: 6" sq., 10" ht.
 Extends 7-1/2". H/CTR 4".
 Lamp: One medium base lamp, 100w max.



P6501-84

P6501-84 Espresso
 Size: 9-1/2" sq., 15-5/8" ht. Overall ht. w/chain 87"; wire 10'.
 Lamp: One medium base lamp, 100w max.



P5996-84

P5996-84 Espresso
 Size: 11" sq., 22-1/4" ht.
 Extends 14". H/CTR 10".
 Lamp: One medium base lamp, 100w max.



P6501-84

P6401-84 Espresso
 Size: 9-1/2" sq., 21-3/8" ht.
 Fits 3" post (order separately).
 Lamp: One medium base lamp, 100w max.

Lamps



MLS13GUSWW6
13w self ballasted squat GU24
lamp. 2700K, 900 lumens



MLS18GUSWW6
18w self ballasted squat GU24
lamp. 2700K, 1250 lumens



MLS24GUSWW
26w self ballasted squat GU24
lamp. 2700K, 1650 lumens



Index

Product No. . . PG

MLS13GUSWW6 . . . 79
 MLS18GUSWW6 . . . 79
 MLS26GUSWW . . . 79

P2000

P2000 56
 P2001 56
 P2002 56
 P2003 56
 P2004 57
 P2005 57
 P2006 57
 P2007 57
 P2008 60
 P2009 60
 P2010 60
 P2011 60
 P2012 54
 P2013 54
 P2014 54
 P2015 54
 P2018 62
 P2019 62
 P2020 62
 P2021 62
 P2612 64
 P2643 64
 P2646 64
 P2650 29, 64
 P2706 58
 P2707 58
 P2708 58
 P2709 58
 P2713 58
 P2714 58
 P2846 61
 P2847 61
 P2848 61
 P2907 60
 P2927 63
 P2998 59

P3000

P3030 63
 P3057 63
 P3058 63
 P3209 7, 55
 P3210 55
 P3223 55
 P3236 55
 P3408 33
 P3410 33
 P3412 33
 P3434 45
 P3550 25
 P3587 18
 P3682 43
 P3798 13
 P3821 29
 P3870 61
 P3878 6
 P3912 29
 P3914 32
 P3928 33
 P3929 33
 P3931 52
 P3932 14

P3937 6
 P3938 5
 P3939 52
 P3941 21, 68
 P3942 21, 68
 P3943 11
 P3944 26
 P3945 26
 P3946 43
 P3947 44
 P3948 13
 P3952 39
 P3953 39
 P3954 42
 P3955 36
 P3956 3
 P3957 2
 P3958 3
 P3959 38
 P3960 46
 P3968 11

P4000

P4440 31
 P4441 31
 P4489 16
 P4490 17
 P4492 19
 P4537 7
 P4539 7
 P4619 23
 P4621 28
 P4622 28
 P4623 30
 P4625 30
 P4626 23
 P4627 32
 P4629 5
 P4632 51
 P4635 51
 P4638 50
 P4641 24
 P4642 25
 P4643 27
 P4644 44
 P4645 45
 P4646 44
 P4648 12
 P4649 12
 P4659 40
 P4660 40
 P4661 42
 P4662 40
 P4663 41
 P4664 34
 P4665 35
 P4666 34
 P4667 35
 P4668 37
 P4669 36
 P4670 38
 P4671 39
 P4672 38
 P4673 48
 P4674 49
 P4675 49
 P4676 47

P4677 46
 P4678 47

P5000

P5004 7
 P5006 39
 P5007 48
 P5008 47
 P5019 5
 P5034 48
 P5044 44
 P5049 8
 P5058 8
 P5059 8
 P5062 13
 P5065 52
 P5105 5
 P5113 33
 P5114 41
 P5118 6
 P5126 11
 P5128 24
 P5129 12
 P5131 37
 P5134 21
 P5164 14
 P5270 16
 P5300 30
 P5449 67
 P5499 68
 P5549 67
 P5589 68
 P5631 67
 P5719 67
 P5728 67
 P5781 65
 P5786 65
 P5819 73
 P5849 68
 P5851 68
 P5906 60
 P5959 78
 P5966 78
 P5967 78
 P5977 74
 P5978 74
 P5979 74
 P5980 75
 P5981 75
 P5982 75
 P5987 76
 P5988 76
 P5989 76
 P5996 78
 P5997 71
 P5998 71

P6000

P6000 72
 P6001 72
 P6002 72
 P6003 70
 P6004 70
 P6005 70
 P6400 72
 P6401 78
 P6402 74

P6403 75
 P6404 76
 P6405 71
 P6406 70
 P6407 77
 P6500 72
 P6501 78
 P6502 74
 P6503 75
 P6504 76
 P6505 71
 P6506 70
 P6507 77
 P6508 77
 P6600 77
 P6601 77
 P6602 66
 P6603 66
 P6604 66
 P6605 66

P7000

P7026 50
 P7027 10
 P7046 44
 P7048 39
 P7049 49, 63
 P7050 46
 P7081 33
 P7153 53

P8000

P8926 50

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL Listed or Classified or CSA Certified unless otherwise noted.

Thomasville Lighting® is manufactured by Progress Lighting under a license from and to the quality and design specifications of Thomasville Furniture Industries, Inc.

Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2012

All rights reserved.
 International Copyright Secured.





Progress Lighting, Inc.

701 Millennium Boulevard
Greenville, SC 29607
www.progresslighting.com

01/12



Hubbell Lighting, Inc.