



2 0 1 5



The products depicted in this catalog are protected by United States Federal and/or State Law, including Patent, Trademark and/or Copyright laws.

Catalog and all elements of catalog design are protected by United States Federal and/or State Law, including Patent, Trademark and/or Copyright laws.

Table of Contents

Table of Contents	1-9	Iconic™	102-103	Supra® 52"	194-197
Welcome	10-11	Lineage™	107	Supra® 52" with Light	192-193
Contemporary Collection		Napoli™	110	Timeless	176-179
Aluma	70-71	Napoli™ II	111	Traditional Mojo	166-167
Artemis™	34-39	Salon Grand™	108	Ultra-Max™	190-191
Artemis™ XL5	56-57	Santa Lucia™	106		
Aviation	28-31	Traditional Mojo	166-167	Economy Collection	
Cirque™	78-79	Volterra™	112-113	Contractor 42"	218-219
Como™	80-81			Contractor 52"	216-217
Concept™ I	66-67	Gyro Collection		Contractor LED	204-205
Concept™ II 44"	64-65	Gyrette™	120	Contractor Plus	206-207
Concept™ II 52"	62-63	Gyro™	118	Contractor Uni-Pack	208-215
Flyte®	72-73	Gyro™ Wet	119, 162	Mesa	220
Gilera	48-51	Traditional Gyro™	115		
Java	68-69, 144-145	Vintage Gyro™	116-117	Finish Guide	221, Fold Out
Kewl	58-59			Fan Control Systems	
Light Wave	44-45	Indoor/Outdoor Collection		Compatibility Chart	224-225
Moda	60-61	Aluma Wet	142-143	Fan Controls	222-223
Pancake	52-53	Concept™ II Wet	146-147		
Raptor	22-23	Concept™ I Wet 52"	124-125	Fan Hanging Systems	
Roto	54-55	Concept™ I Wet 58"	122-123	Accessories	228
Sabot	24-25	Craftsman™	128	Downrods	226-227
San Francisco®	74-75	Gauguin™	154-155		
Slipstream	32-33	Gyro™ Wet	119, 162	Light Kits	
Slipstream XXL	132-137	Java	68-69, 144-145	Custom Light Kits	235
Spectre	12-15	Magellan®	140-141	Universal Light Kits	229-234
Symbio	26-27	Rainman™	130-131		
Uchiwa	76-77	Shangri-La®	129	Accessory Fan Blades	236-237
Wave	46-47	Slipstream	32-33	Glass Shades	238-239
Wing	40-43	Slipstream XXL	132-137	Bulb Reference	240
Zen	82-83	Strata	138-139	Index	241-243
		Sundance™	160-161		
Transitional Collection		Sundowner®	156-159	Room Size & Ceiling Height	
Airus™	84-85	Sunseeker	126-127	Recommendations	244
Delano®	94-95	Terrana	152-153	Dimensions & Specifications	
Delano® II	96-97	Traditional Concept™ 44"	88-89,		
New Era	92-93	150-151		
Spacesaver	90-91	Traditional Concept™ 52"	86-87,		
Traditional Concept™ 44"	88-89,	148-149		
.	150, 151				
Traditional Concept™ 52"	86-87,	Value Collection			
.	148, 149	Bolo™	174-175		
		Classica	188-189		
Retro Collection		Dyno	164-165		
Acero™	98-99	Hilo	172-173		
Hassock Aire	101	Kafé	186-187		
Retro Style Fan	100	Kafé-XL	184-185		
Xtreme	16-21	Kola	182-183		
		Kola-XL	180-181		
Traditional Collection		Mojo	168-169		
Calais™	114	Mojo II	170-171		
Cristafano™	109	Supra® 32"	202-203		
Great Room Traditional	104-105	Supra® 44"	200-201		
		Supra® 44" with Light	198-199		

Ceiling Fans



Acero™
F601
Pages 98-99



Airus™
F598
Pages 84-85



Aluma
F521
Pages 70-71



Aluma Wet
F523
Pages 142-143



Artemis™
F803
Pages 34-39



Artemis™ XL5
F905
Pages 56-57



• **Aviation**
F853
Pages 28-31



Bolo™
F620
Pages 174-175



Calais™
F544
Page 114



Cirque™
F596
Pages 78-79



• **Classica**
F659
Pages 188-189



Classica - Gallery Edition
F759
Page 188

Ceiling Fans



Como™
F603
Pages 80-81



Concept™ I 44"
F516
Pages 66-67



Concept™ I 52"
F517
Pages 66-67



Concept™ I Wet 52"
F476 / F577
Pages 124-125



Concept™ I Wet 58"
F477
Pages 122-123



Concept™ II 44"
F518
Pages 64-65



Concept™ II 52"
F519
Pages 62-63



Concept™ II Wet 52"
F474 / F574
Pages 146-147



Contractor 42"
F546
Pages 218-219



Contractor 52"
F547
Pages 216-217



• • **Contractor LED**
F556L
Pages 204-205



• • **Contractor Plus**
F556
Pages 206-207

Ceiling Fans



Contractor Uni-Pack
F548
Pages 212-215



Contractor Uni-Pack
F647
Pages 208-209



Contractor Uni-Pack
F648
Pages 210-211t



Craftsman™
F840
Page 128



Cristafano™
F900
Page 109




Delano®
F701
Pages 94-95




Delano® II
F711
Pages 96-97



• **Dyno**
F1000
Pages 164-165



Flyte®
F531
Pages 72-73



Gauguin™
F581
Pages 154-155



Gilera
F733
Pages 48-51



Great Room Traditional
F539
Pages 104-105

Ceiling Fans



Gyrette™
F302
Page 120




Gyro™
F602
Page 118



Gyro™ Wet
F402
Page 119, 162



Haddock Aire
F315
Pages 101



• **Hilo**
F470
Pages 172-173



Iconic™
F672
Pages 102-103



Java
F753
Pages 68-69, 144-145



• **Kafé**
F695
Pages 186-187



• **Kafé-XL**
F696
Pages 184-185



• **Kewl**
F833
Pages 58-59



• **Kola**
F688
Pages 182-183



• **Kola-XL**
F689
Pages 180-181

Ceiling Fans



• **Light Wave**
F844
Pages 44-45



Lineage
F812
Pages 107



Magellan®
F579
Pages 140-141



Mesa™
F565 / F566
Pages 220



Moda
F737
Pages 60-61



Mojo
F522
Page 168-169



• **Mojo II**
F533
Pages 170-171



Napoli™
F705
Page 110



Napoli™ II
F715
Page 111



New Era
F513
Pages 92-93



• **Pancake**
F738
Pages 52-53



Rainman™
F582
Pages 130-131

Ceiling Fans



• • **Raptor**
F617
Pages 22-23



Retro Style Fan
F300
Page 100



• **Roto**
F524
Pages 54-55



• • **Sabot**
F745
Pages 24-25



Salon Grand™
F707
Page 108



San Francisco®
F528 / F529
Pages 74-75



Santa Lucia™
F820
Page 106



Shangri-La®
F580
Page 129



Slipstream
F888
Pages 32-33



• **Slipstream XXL**
F889
Pages 132-137



Spacesaver
F510
Pages 90-91



• • **Spectre**
F726
Pages 12-15

Ceiling Fans



Strata
F734
Pages 138-139



• **Sundance™**
F571 / F572
Pages 160-161



• **Sundowner®**
F589
Pages 156-159



• **Sunseeker**
F532
Pages 126-127



Supra® 32"
F562
Pages 202-203



Supra® 44"
F563
Pages 200-201



Supra® -SP 44"
F563-SP
Pages 198-199



• **Supra® 52"**
F568
Pages 194-197



Supra® 52"
F569
Pages 192-193



• • **Symbio**
F828
Pages 26-27



Terrana
F680
Pages 152-153



• **Timeless**
F614
Pages 176-179

Ceiling Fans



Traditional Concept™ 44"
F593
Pages 88-89, 150-151



Traditional Concept™ 52"
F594
Pages 86-87, 148-149



Traditional Gyro™
F502
Pages 115



• **Traditional Mojo**
F622
Pages 166-167



Uchiwa
F824
Pages 76-77



• **Ultra-Max™**
F588
Pages 190-191



Vintage Gyro™
F802
Pages 116-117




Volterra™
F702
Pages 112-113



• **Wave**
F843
Pages 46-47




• **Wing**
F823
Pages 40-43



• **Xtreme**
F887
Pages 16-21



• **Zen**
F514
Pages 82-83



Aviation - F853
Page(s): 28

Minka-Aire® invites you to view our ceiling fan collection designed for today's varying lifestyles.

Within this catalog, you will find designs of contemporary flair with elegant grace, transitional timeless styles and a collection from our licensed design series.



San Francisco® - F529
Page(s): 74

The architectural trend toward Great Rooms has led Minka-Aire® to redesign some of our most popular styles with enlarged bodies and longer blades to circulate more air and complement the spaciousness of these rooms.

Our Outdoor Series of fans allows your friends and family to enjoy outdoor dining or time in your spa while continuing to have pleasant surroundings.

We offer many design choices for the outdoors; rated for

all-weather exposure.

Minka-Aire® ceiling fans offer a wide variety of designs for the American home.



Timeless - F614
Page(s): 176

Our Products Feature:

- Finishes that complement today's interiors and exteriors
- Advanced technology with our control systems
- Ease of installation
- Limited Lifetime Warranty on our motors
- Wide variety of unique designs from sleek contemporary to classic traditional
- Powerful motors that conserve energy use in the home
- Flawless craftsmanship
- Designs that coordinate with our Minka-Lavery® lighting collections



Gauguin™ - F581
Page(s): 154

- Safe  and  manufacturing approval products

Our energy-saving Minka-Aire® ceiling fans are manufactured to the highest quality standards.

We are privileged to partner with some of the most recognized designers in the home furnishing industry. The products under our Designer Collection features George Kovacs®, Hearst Castle® and Jessica McClintock Home, The Romance Collection™. Our Designer Collection combines a unique blend of style with performance. All of these designs exemplify elegance and a timeless spirit that is the hallmark of Minka-Aire®.



Spectre

with LED Light

LED



F726-BN/SL

Brushed Nickel Finish
Silver Blades
with Clear Lens

LED

Features:

- 14° Blade Pitch
- 60" 4 Blades
- DC 188 x 10MM Motor
- 3½" and 6" Downrods
- Integrated LED Light
Uses 18W LED (Included)
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Special Hand Held Remote Control
System Included - RC400

U.S. Patent(s): Pending

* Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,000	82	187.5

* Estimated



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Versatile, industrial styling and creative details are the key to Spectre. The distinctive blade irons hug the fan body, providing a unique look compatible with contemporary environments.

LED

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

LED



F726-WHF/BN

Flat White / Brushed Nickel Finish
Flat White Blades
with Clear Lens



F726-BN/ORG

Brushed Nickel / Orange Finish
Orange Blades
with Clear Lens

LED

Spectre

with LED Light

LED

F726-ORB/AB

Oil Rubbed Bronze with
Antique Brass Finish
Tobacco Blades
with Clear Lens

LED

Features:

- 14° Blade Pitch
- 60" 4 Blades
- DC 188 x 10MM Motor
- 3½" and 6" Downrods
- Integrated LED Light
Uses 18W LED (Included)
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Special Hand Held Remote Control
System Included - RC400

U.S. Patent(s): Pending

* Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,000	82	187.5

* Estimated



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

LED

F726-WHF/BN

Flat White / Brushed Nickel Finish
Flat White Blades
with Clear Lens

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

GEORGE
KOVACS®

by

minkaAire®
A Minka Group® Co.

LED

F726-ORB/BN


Oil Rubbed Bronze / Brushed Nickel Finish
Oil Rubbed Bronze Blades
with Clear Lens

Versatile, industrial styling and creative details is the key to Spectre. The distinctive blade irons hug the fan body, providing a unique look compatible with contemporary environments.


LED

LED

Xtreme



This industrial size fan lends itself to almost any setting. Xtreme's clean, sleek, contemporary design with a DC motor and a choice of blade sizes makes it perfect for large areas.



F887-72-BN 72"
F887-80-BN 80"
F887-88-BN 88" (Shown)
F887-96-BN 96"

□ Brushed Nickel Finish
 Silver Blades



RC400

□ Full Function Hand Held Remote Control Included
 For Details See Page(s): <?>

Features:

- 4° Blade Pitch
- 72", 80", 88" or 96" 9 Blades
- DC 165 x 25mm Motor
- 3½" and 6" Downrods
- Aluminum Blades
- Install with Blades at least 10' from the Floor
- Special Hand Held Remote Control System Included - RC400

Energy Information for 72"
 (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
10,203	29	351.83

Lifetime
 WARRANTY


Remote
 CONTROL
 FULL FUNCTION

Xtreme






Xtreme



This industrial size fan lends itself to almost any setting. Xtreme's clean, sleek, contemporary design with a DC motor and a choice of blade sizes makes it perfect for large areas.



F887-72-ORB 72"
F887-80-ORB 80"
F887-88-ORB 88" (Shown)
F887-88-ORB 96"

Oil Rubbed Bronze Finish
 Oil Rubbed Bronze Blades

Features:

- 4° Blade Pitch
- 72", 80", 88" or 96" 9 Blades
- DC 165 x 25mm Motor
- 3½" and 6" Downrods
- Aluminum Blades
- Install with Blades at least 10' from the Floor
- Special Hand Held Remote Control System Included - RC400

Energy Information for 72"
 (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
10,203	29	351.83



RC400

Full Function Hand Held Remote Control Included
 For Details See Page(s): <?>

Lifetime
 WARRANTY

Remote
 CONTROL
 FULL FUNCTION



LED

LED

F617-GM

Gun Metal Finish
Gun Metal Blades
with Etched Opal Glass

This contemporary design is coupled with the energy saving advancements of DC motor technology and an integrated LED light source.

LED



F617-WH

White Finish
White Blades
with Etched Opal Glass

Raptor


with LED Light

LED



F617-ORB/AB

Oil Rubbed Bronze / Antique Brass Finish
Tobacco Blades
with Tinted Opal Glass



F617-BN

Brushed Nickel Finish
Silver Blades
with Etched Opal Glass

LED

Features:

- 14° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- DC 172 x 12mm Motor
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Special Hand Held Remote Control System Included - RC600

*** Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,000	30	200

* Estimated

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC600

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Sabot

with LED Light

LED

LED



F745-DK

Distressed Koa Finish
Reversible Medium Maple / Dark Walnut Blades
with White Lens
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 52" 5 Blades
- DC 172 x 12mm Motor
- 3½" and 6" Downrods
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Special Hand Held Remote Control
System - RC600

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,000	30	166.6



RC600

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Sabot's sleek, contemporary design has created a vision for today's interiors. Its low profile provides maximum air management in rooms with minimal ceiling heights.

The Sabot's integrated, energy efficient LED light will bring any room to life.

LED

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

LED



LED

F745-BN

Brushed Nickel Finish
Silver Blades
with White Lens



F745-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with White Lens
(Shown with Dark Walnut Blades)

LED

Symbio

with LED Light

Contemporary
Contemporary

LED



F828-BN

Brushed Nickel Finish
Silver Blades
with Etched Glass

LED



F828-ORB

Oil Rubbed Bronze
Medium Maple Blades
with Tea Stain Glass

LED



F828-WHF

Flat White Finish
Flat White Blades
with Etched Glass

LED

F828-BN/DW

Brushed Nickel Finish
Dark Walnut Blades
with Etched Glass

LED

This clean contemporary powerhouse delivers the air flow of larger fans using DC motor technology to keep energy consumption to a minimum while the integrated LED light provides energy efficient illumination.

Features:

- 13° Blade Pitch
- 56" 5 Blades
- 3½" and 6" Downrods
- Integrated LED Light
Uses 16W DC LED (Included)
3 Year Warranty
- 1352 Lumens
- 2700K
- CRI 80
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): Pending

*** Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,000	35	171

* Estimated

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

F828-BN/WH

Brushed Nickel Finish
White Blades
with Etched Glass

LED

Aviation

F853-BN/DK

Brushed Nickel Finish
Distressed Koa Blades

Features:

- Variable Blade Pitch
- 60" 3 Blades
- DC 120 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D721,429; D721,800; D726,298

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,604	25.92	254.80

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC500

Full Function Hand Held Remote Control Included
For Details See Page(s): 222



Inspired by the classic form of vintage aircraft propellers, our Aviation fan has an updated appeal that addresses a new audience with sleek, elegant lines and a combination of finish techniques that work for all of today's trends.

F853-RW

Rosewood Finish
Rosewood Blades

Aviation

F853-WH

White Finish
White Blades

Features:

- Variable Blade Pitch
- 60" 3 Blades
- DC 120 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D721,429; D721,800; D726,298

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,604	25.92	254.80

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC500

Full Function Hand Held Remote Control Included
For Details See Page(s): 222





F853-BN/MM

Brushed Nickel Finish
Medium Maple Blades



F853-BN/SL

Brushed Nickel Finish
Silver Blades

Slipstream



F888-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Features:

- 14° Blade Pitch
- 65" 8 Concave Blades
- DC 165 x 25mm Motor
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Special Hand Held Remote Control
System Included - RC400
- Integrated Light
Uses 1-18W GU24 Non-Dimmable
Squat CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
8,778	27.6	318.04

Slipstream's sleek industrial styling
destines this 8-bladed
wonder to make a cool
statement in any indoor or
outdoor setting.

U.S. Patent(s): D715,917



LISTED
For Wet Location






F888-WHF

Flat White Finish
Flat White Blades
with Etched Opal Glass



F888-DK

Distressed Koa Finish
Distressed Koa Blades
with Tinted Opal Glass



F888-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Shown with Cap for Non-Light Use

Artemis™



F803-DK
 Distressed Koa Finish
 with Tinted Opal Glass

Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 58" 3 Vanes
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
 Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387;
 D535,388; D536,083; 7,481,626

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



F803-LN
 Liquid Nickel Finish
 with Etched Opal Glass



WCS212
 Full Function Wall Control System Included
 For Details See Page(s): 223


Lifetime
 WARRANTY

WallControl
 FULL FUNCTION

GEORGE
KOVACS®

by

minkaAire®
A Minka Group® Co.



The distinct profile of the Artemis™ is captured by the Flying Vanes™ that incorporate the fan housing. A true design statement!

Winner of the 2005 Chicago Athenaeum: Museum of Architecture and Design's Good Design Award.



F803-MG

Mahogany Finish
with Etched Opal Glass

Artemis™



F803-RD

High Gloss Pure Red Finish with Etched Opal Glass

Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 58" 3 Vanes
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387; D535,388; D536,083; 7,481,626

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F803-CPBR


Copper Bronze Finish
with Tinted Opal Glass



F803-SL

Silver Finish
with Etched Opal Glass

Artemis™



F803-WH

High Gloss White Finish
with Etched Opal Glass

Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 58" 3 Vanes
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387;
D535,388; D536,083; 7,481,626

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

F803-TL

Translucent Finish
with Etched Opal Glass

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F803-BK

High Gloss Black Finish
with Etched Opal Glass



F803-MP

Maple Finish
with Etched Opal Glass

Wing



F823-DK
Distressed Koa Finish



Features:

- Variable Blade Pitch
- 52" 1 Wing
- DC 125 x 30mm Motor
- 6" Downrod
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): D678,977; 9,004,863

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,974	30.2	197.81

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 222



A unique 52" single wing fan that transcends all conventional designs.

Winner of the 2010 Chicago
Athenaeum: Museum of Architecture
and Design's Good Design Award.

F823-WH

High Gloss White Finish

Wing

F823-MG

Mahogany Finish

Features:

- Variable Blade Pitch
- 52" 1 Wing
- DC 125 x 30mm Motor
- 6" Downrod
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): D678,977; 9,004,863

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,974	30.2	197.81

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC400


Full Function Hand Held Remote Control Included
For Details See Page(s): 222





□ **F823-SL**

Silver Finish



□ **F823-MP**

Maple Finish

Light Wave

with LED Light

LED

LED



F844-DK

Distressed Koa Finish
Distressed Koa Blades
with Etched Lens

Features:

- 48° Blade Pitch
- 52" 3 Blades
- 4½" and 6" Downrods
- Integrated Light
Uses 17W Dimmable LED
(Included) 3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Hand Held Remote Control System
- Replacement LED Assembly
(Part #6F844LK01)

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,024	65.3	76.94



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222

Light Wave is the next generation of our highly successful, ground-breaking Wave fan. Its energy-efficient LED* light source integrates light without compromising design.

LED

Lifetime
WARRANTY

Remote
CONTROL

LED

F844-WH


White Finish
White Blades
with Etched Lens



F844-SL

Silver Finish
Silver Blades
with Etched Lens

Wave



F843-SL

Silver Finish

Features:

- 48° Blade Pitch
- 52" 3 Blades
- 4½" and 6" Downrods
- Hand Held Remote Control System

U.S. Patent(s): D715,419; D715,421

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,580	66.4	99

A truly unique design that draws inspiration from the ocean's graceful and tubular wave formations.

Lifetime
WARRANTY


Remote
CONTROL



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222





F843-DK
Distressed Koa Finish



F843-WH
White Finish

Gilera



F733-BK/RW

Black / Rosewood Finish
Rosewood Blades

Features:

- 14° Blade Pitch
- 62" 3 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,431	102.8	62.55



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Vintage Italian racing motorcycles served as the design vision for the Gilera ceiling fan. With its 62-inch blade, Gilera is specially designed for use in rooms with greater ceiling heights. Highly detailed and dramatically proportioned, Gilera is destined to become an heirloom of the future.

F733-SL

Silver Finish
Silver Blades

Gilera



F733-BS/BN

- Brushed Steel / Brushed Nickel Finish
Medium Maple Blades

Features:

- 14° Blade Pitch
- 62" 3 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,431	102.8	62.55



WCS212

- Full Function Wall Control System Included
For Details See Page(s): 223

F733-PN

- Polished Nickel Finish
Silver Blades

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F733-WH

- White Finish
- White Blades



Pancake



F738-BN

Brushed Nickel Finish
Silver Blades

Features:

- 12° Blade Pitch
- 52" 4 Blades
- **6" Internally Threaded Downrod**
Downrod sizes of 48", 60" and 72" are currently not available in BN and PN finishes.
See Page(s): 228 for Details
- Max Ceiling Slope Angle 18°
- Full Function Hand Held Remote Control System

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,405	63.9	84.58



F738-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 223





F738-DK

Distressed Koa Finish
Distressed Koa Blades

Our Pancake ceiling fan magically houses all the needed components of a high performance ceiling fan into a slim 3-inch deep body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room.



F738-WHF

Flat White Finish
Flat White Blades

Roto



F524-ABD

Brushed Aluminum Finish
Silver Blades

Features:

- 22° Blade Pitch
- 52" 3 Blades
- 3½" and 6" Downrods
- Aluminum Construction
- 2-Wire Installation Wall Control
Converts to Electronic Control
System

U.S. Patent(s): Pending

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,816	51.5	113

Lifetime
WARRANTY

WallControl



WC105-WH

Wall Control System Included
For Details See Page(s): 223


Roto features a sleek and contemporary design with a classic industrial look. Well edited and an impeccably executed design features a slight "fold" construction along the length of the blades to increase the flow of air. A perfect marriage of form and function.



F524-WHF
Flat White Finish
Flat White Blades



F524-DK
Distressed Koa Finish
Distressed Koa Blades




F524-ORB
Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades

GEORGE
KOVACS®

by

minkaAire®
A Minka Group® Co.



F905-SL

Silver Finish
with Etched Opal Glass

Features:

- Variable Blade Pitch
- 62" 5 Blades
- DC 172 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC600
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D721,430

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
8,289	41.48	199.83

The big brother of our original Artemis™, the distinct profile of the Artemis™ XL5 is captured by the five Flying Vanes™ that encase the fan housing - creating a true design statement!



RC600

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Lifetime
WARRANTY


Remote
CONTROL
FULL FUNCTION

Artemis™ XL5



F905-DK

Distressed Koa Finish
with Tinted Opal Glass



F905-WH

White Finish
with Etched Opal Glass

Shown with Cap for Non-Light Use

Kewl



□ **F833-RD**
Red Finish

Features:

- 22° Blade Pitch
- 52" 3 Blades
- 3½" and 6" Downrods
- 2-Wire Installation Wall Control
Converts to Electronic Control System

U.S. Patent(s): D715,418; D726,299

Special Note:


- Custom Finish Orders Accepted
 - 200 Piece Minimum Order Per Finish
 - 90 Day Lead Time

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,304	55	114.62



□ **WC105-WH**
Wall Control System Included
For Details See Page(s): 223



□ **F833-WH**
White Finish

Lifetime
WARRANTY

WallControl





F833-SL
Silver Finish



F833-BK
Black Finish



Moda



F737-BN

Brushed Nickel Finish
Silver Blades
with Etched White Glass

Features:

- 20° Blade Pitch
- 60" 3 Blades
- DC 188 x 14mm Motor
- 3½" and 6" Downrods
- Integrated Uplight
Use 10-15W Candelabra Bulbs
(Included)
- Special Hand Held Remote Control
System Included - RC500

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,458	26.5	281.43



F737-ORB

Oil Rubbed Bronze Finish
Dark Maple Blades
with Tea Stained Glass



RC500

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

Versatility, transitional styling and creative details are the key to Moda. With hand-crafted blades, which uniquely hug close to the hub, Moda incorporates a tinted glass shade that directs light up toward the ceiling, producing a glowing up-light effect.



F737-WH

White Finish
White Blades
with Etched White Glass

Concept™ II

52"

F519-BN

Brushed Nickel Finish
Silver Blades
with White Opal Glass

F519-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with White Opal Glass

F519-PN

Polished Nickel Finish
Silver Blades
with White Opal Glass



F519-WH

White Finish
White Blades
with White Opal Glass

As the name implies, “a taste of things to come,” simple in style, yet ingenious by design, the Concept™ II requires 75% less time and labor to assemble than conventional ceiling fans.

Features:

- 14° Blade Pitch
- 52" 3 Concave Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 11½" with or without Light
- Full Function Hand Held Remote Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,710	55	103.82



F519-MG

Mahogany Finish
Mahogany Blades
with White Opal Glass

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Accessory Blades Available. See Page(s): 236

Concept™ II

44"



F518-WH

White Finish
White Blades
with White Opal Glass

As the name implies, "a taste of things to come," simple in style, yet ingenious by design, the Concept™ II requires 75% less time and labor to assemble than conventional ceiling fans.



F518-BN

Brushed Nickel Finish
Silver Blades
with White Opal Glass



F518-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with White Opal Glass



F518-PN

Polished Nickel Finish
Silver Blades
with White Opal Glass
Shown with Cap for Non-Light Use

Features:

- 14° Blade Pitch
- 44" 3 Concave Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 11½" with or without Light
- Full Function Hand Held Remote Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,071	43.7	93.16

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RGS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Accessory Blades Available. See Page(s): 236



F516-ORB 44"

F517-ORB 52"

Oil Rubbed Bronze Finish
Taupe Blades
with White Opal Glass



F516-WH 44"

F517-WH 52"

White Finish
White Blades
with White Opal Glass

Concept™ I

F516-PN 44"
F517-PN 52"

Polished Nickel Finish
Silver Blades
with White Opal Glass



F516-BN 44"
F517-BN 52"

Brushed Nickel Finish
Silver Blades
with White Opal Glass

Shown with Cap for Non-Light Use



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Features:

- 14° Blade Pitch
- 44" or 52" 3 Concave Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;
D478,980; 7,008,192

F516 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,987	46	86.68

F517 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,028	61	98.82

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

Accessory Blades Available. See Page(s): 236

Java



F753-KA

Kocoa Finish
Kocoa Blades



F753-BNW

Brushed Nickel Wet Finish
Silver Blades

Features:

- 14° Blade Pitch
- 54" 3 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Indoor/Outdoor Use
UL Listed for Wet Locations

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,681	60	94

Lifetime
WARRANTY

Remote
CONTROL



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222



LISTED

For Wet Location





F753-PN

Polished Nickel Finish
Silver Blades
(Finish For Indoor Use Only)

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.



F753-WHF

Flat White Finish
Flat White Blades

Aluma



F521-ABD

Brushed Aluminum Finish
Silver Blades
with Etched Opal Glass

Features:

- 12° Blade Pitch
- 52" 4 Blades
- 3½" and 6" Downrods
- WC106 4-Speed Full Range Dimmer
3-Wire Installation Wall Control
Converts to Electronic Control System
- All Aluminum Construction
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,471	66.6	82.15



WC106-WH

Wall Control System Included
For Details See Page(s): 223



F521-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Lifetime
WARRANTY

WallControl

With its 4-speed control, full range dimmer, 52-inch sweep, halogen light and optional cap for non-light use, the Aluma is minimal in form with a youthful soft contemporary twist that makes it a fan with universal appeal.



F521-WHF

Flat White Finish
Flat White Blades
with Etched Opal Glass
Shown with Cap for Non-Light Use



F531-L-BN

Brushed Nickel Finish
Birdseye Maple Blades
with White Opal Glass



F531-L-WH

White Finish
High Gloss White Blades
with White Opal Glass



F531-L-BN/MG

Brushed Nickel Finish
Mahogany Blades
with White Opal Glass
Mahogany Downlink™

Shown with Cap for Non-Light Use

The essence of simplicity and elegance, the Flyte® fan's combination of integrated halogen light and distinctive hanging system gives this contemporary design a compelling and sophisticated presence.

Winner of the 2001 Chicago Athenaeum: Museum of Architecture and Design's Good Design Award

Features:

- 14° Blade Pitch
- 56" 3 Blades
- Includes 9" Downlink™ Hanging System with ½" I.D. Downrod
- Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Suitable for Installation on Vaulted Ceilings up to 21°
- Capable of using 3½" Downrod for Low Ceiling Application (Part #DR235-44 and #DR235-BN)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D453,216

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,703	67	85.12



WCS213

Wall Control System Included
For Details See Page(s): 223

Lifetime WARRANTY WallControl

Accessory Blades Available. See Page(s): 236

Additional Downlink™ Options Available
See Page(s): 228

Winner of the 1998 Chicago
Athenaeum: Museum of Architecture
and Design's Good Design Award

F529-L-ORB

- Oil Rubbed Bronze Finish
- Medium Maple Blades
- with Tinted Opal Glass

F528-L-BS/CH

- Brushed Steel / Chrome Finish
- Birdseye Maple Blades

San Francisco®



F529-L-BS/CH

Brushed Steel / Chrome Finish
Birdseye Maple Blades
with Frosted Glass

The bold, clean lines and simplicity of the San Francisco® fan make it a timeless architectural design element, suited for any interior.

Features:

- 13° Blade Pitch
- 56" 3 Blades
- Includes 12" Pre-Wired Downbridge™ Hanging System
- Wall Control System
- Integrated Halogen Light Uses 1-75W JDR Intermediate Base Bulb (Included)
- Suitable for Installation on Vaulted Ceilings up to 30°

U.S. Patent(s): 5,951,253; 6,158,964; 6,171,060; 6,250,885

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,780	77	75.02



WCS213

Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY **WallControl**

Accessory Blades Available. See Page(s): 236

Additional Downbridge™ Options Available.
See Page(s): 228

Uchiwa



F824-ORB/TB

Oil Rubbed Bronze / Toned Brass Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

うちわ

Harmoniously marked by characteristics and finishes of the present period, the Uchiwa is a functional art piece.

Features:

- 16° Blade Pitch
- 56" 3 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-75W Mini-Can Halogen Bulb (Included)

U.S. Patent(s): D618,786; D618,787; D620,586

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,574	58	78.86



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Lifetime WARRANTY

WallControl FULL FUNCTION



F824-BK/CH

Black / Chrome Finish
Silver Blades
with Etched Opal Glass



F824-WH

White Finish
White Blades
with Etched Opal Glass

by



F596-BN

Brushed Nickel Finish
Silver Blades

Winner of the 2003 Chicago
Athenaeum: Museum of Architecture
and Design's Good Design Award

Features:

- 14° Blade Pitch
- 54" 3 Blades and 25" 3 Blades
- 4" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-50W MR16 120V 2-Pin
Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D510,621; D513,316; D514,689;
D524,433; D549,816

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,087	49	103.81



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



F596-BN

Brushed Nickel Finish
Shown with Optional FB196-MG Blades

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Accessory Blades Available. See Page(s): 236

Cirque™



F596-PN/TL

Polished Nickel Finish
Translucent Blades



F596-BN

Brushed Nickel Finish
Shown with Optional FB196-RYB Blades



F603-ORB

- Oil Rubbed Bronze Finish
Tobacco Blades
with Satin White Opal Glass



F603-WH

- White Finish
White Blades
with Satin White Opal Glass

Como™



F603-BN

Brushed Nickel Finish
Silver Blades
with Satin White Opal Glas

Como™ is a harmonious, versatile design with clean, contemporary lines highlighted with subtle chrome, bronze and brushed nickel accents.

Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-75W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D476,728

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,761	92	73.29



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223





F514-ORB

- Oil Rubbed Bronze Finish
- Medium Maple Blades
- with Tinted Opal Glass



F514-BN

- Brushed Nickel Finish
- Silver Blades
- with White Frosted Glass
- Shown with Optional Cap for Non-Light Use

Zen



F514-WH

White Finish
White Blades
with White Frosted Glass

A clean modern profile is accentuated in three finish options.

Features:

- 14° Blade Pitch
- 52" 4 Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Integrated Light Kit
Uses 2-13W Non-Dimmable GU24 CFL Bulbs (Included)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,148	71	86.05



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



Airus™



F598-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Excavation Glass

Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System Independent Up/Downlight
- Integrated Halogen Uplight and Downlight
- Uses 4-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D471,269; D473,639; D475,776

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,668	82	69.12



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Airus™ is poetry in motion. Its graceful silhouette comfortably fits in any transitional setting. Featured uplight can be controlled independently of the halogen light below.

Lifetime WARRANTY

WallControl FULL FUNCTION



□ **F598-WH**

White Finish
High Gloss White Blades
with Acid Etched Glass



□ **F598-BN**

Brushed Nickel Finish
Silver Blades
with Acid Etched Glass

Traditional Concept™ 52"



F594-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass

Features:

- 14° Blade Pitch
- 52" 3 Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 10 3/4"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,565	60.5	108.58

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



LISTED

For Wet Location





F594-PW

Pewter Finish
Dark Maple Blades
with Opal Glass



F594-WH

White Finish
White Blades
with Opal Glass

Traditional Concept™ 44"



F593-PW

Pewter Finish
Dark Maple Blades
with Opal Glass

Features:

- 14° Blade Pitch
- 44" 3 Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 10¾"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,940	49	100

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



For Wet Location





F593-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass



F593-WH

White Finish
White Blades
with Opal Glass

Shown with Cap for Non-Light Use



F510-BS

- Brushed Steel Finish
Silver Blades
with Etched Opal Glass



F510-WH

- White Finish
White Blades
with Etched Opal Glass

Spacesaver



F510-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Contemporary styling and superb air circulation for those smaller spaces in your home; perfect for kitchens and food preparation areas, bathrooms, walk-in closets and hallways.

Features:

- 14° Blade Pitch
- 26" 3 Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 10¾"
- 4-Speed Fan
Full Range Dimmer
3-Wire Installation Wall Control
Converts to Electronic Control
- Integrated Halogen Light
Uses 1-50W Mini-Can Halogen Bulb (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
2,132	30	71.07



WC110-WH

Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl



F513-BN

Brushed Nickel Finish
Dark Walnut Blades

Features:

- 14° Blade Pitch
- 52" 4 Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- ENERGY STAR® Light Kits Available (Part #K9380-1 and #K9380-2 Page(s): 229)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,230	73	85.25



F513-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222



New Era

Traditional in styling, yet defined by simple, soft lines.



□ **F513-WH**

White Finish
White Blades



□ **F513-KA**

Kocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)



F701-PW

Pewter Finish
Natural Walnut Blades
with Etched Marble Glass

Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Wall Control System
Independent Up/Downlight
- Integrated Uplight
Use 6-15W Candelabra Bulbs
(Included)
- Integrated Halogen Downlight
Uses 2-50W Mini-Can Halogen
Bulbs (Included)

U.S. Patent(s): D453,218; D457,235; D458,363

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,278	72	73.31



F701-DRB

Dark Restoration Bronze™ Finish
Dark Walnut Blades
with Rustic Scavo Glass



WCS213

Wall Control System Control Included
For Details See Page(s): 223

Lifetime WARRANTY **WallControl**

Delano®

F701-PN

Polished Nickel Finish
Silver Blades
with White Frosted Glass

F701-KA

Kocoo Finish
Reversible Toned Medium Maple / Dark Walnut Blades
with Rustic Scavo Glass
(Shown with Toned Medium Maple Blades)

F701-DRF

Driftwood Finish
Driftwood Blades
with Bone White Glass

Delano® II



F711-DRB

Dark Restoration Bronze™ Finish
Dark Walnut Blades
with Rustic Scavo Glass

Features:

- 14° Blade Pitch
- 52" 5 Blades
- Flush Mount - Ideal for Low Ceilings
Less than 11" Drop from Ceiling
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D595,403; D597,655

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,367	69.5	77



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F711-PN

Polished Nickel Finish
Silver Blades
with White Frosted Glass



F711-PW

Pewter Finish
Natural Walnut Blades
with Etched Marble Glass

Acero™

Winner of the 1999 Chicago Athenaeum: Museum of Architecture and Design's Good Design Award



F601-BS/MG

Brushed Steel / Mahogany Finish
Mahogany Blades
with Opal Frosted Glass

Features:

- 14° Blade Pitch
- 52" 3 Blades (Concave Style)
- 3½" and 6" Downrods
- Unique Wire Form Design
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D461,553; 6,354,801; 6,517,316

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,465	69	93.69



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



F601-BS/BN

Brushed Steel / Brushed Nickel Finish
Silver Blades
with Opal Frosted Glass

Shown with Cap for Non-Light Use

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F601-PN

- Polished Nickel Finish
- Silver Blades
- with Opal Frosted Glass

An evolution of form and function merging today's technology with retro styling, this fan comes with an integrated light.



F601-ORB


- Oil Rubbed Bronze Finish
- Aaron Mahogany Blades
- with Opal Frosted Glass

Portable Series

A special series of fans that go where you go. These portable fans offer the same style, quality and value you expect from Minka-Aire® in a compact and portable design.

Retro Style Fan

An accent that is reminiscent of times past, our Retro Style Fan is your quiet companion; a stylistic, subtle, tabletop solution for your comfort needs in any room.



F300-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades



F300-BN

Brushed Nickel Finish
Brushed Nickel Blades

Features:

- 10" 4 Blade Turbofan
- 3 Speeds: 1,250, 1,400 and 1,500 R.P.M.
- Oscillates 70° Side to Side
- Manual Tilt
- Portable (Net Weight 7lbs.)
- 72" Heavy Duty Cord Length
- Steel Construction
- One Year Limited Warranty

Hassock Aire

Our 1950s-inspired replica of a classic portable floor fan, Hassock Aire has been created with a wink to the past and a nod to the future; it is a nostalgic reminder of simpler times where multi-tasking items were a must. Hassock Aire has three speeds and is designed to gently circulate air in any room, even bringing fresh air in from an open window. Ideal for use in areas of the home where indirect air flow is preferred, such as nursery, home office or bedroom. As a plus, Hassock Aire can be used as an ottoman, providing extra seating or a place to rest your feet.

F315-KA

Kocoa Finish
Black Fins



F315-SL

Silver Finish
Black Fins

Features:

- 12" 3 Blade Turbofan
- 3 Speeds
- Portable (Net Weight 16.31lbs.)
- 112" Cord
- 14" Overall Height
- Supports up to 400lbs.
- UL Listed
- Two Year Limited Warranty



F672-WH/BN

White / Brushed Nickel Finish
White Blades
with Acid Etched Glass

Shown with Cap for Non-Light Use

Features:

- 14° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- Integrated Halogen Light
Uses 1-50W GU10 Halogen Bulb
(Included)
- Hand Held Remote Control
- Cap for Non-Light Use (Included)

U.S. Patent(s): Pending

*** Energy Information (Excludes Lights)**

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,894	75	80

Lifetime
WARRANTY

Remote
CONTROL



RCS212

Hand Held Remote Control Included
For Details See Page(s): 222



F672-ORB

Oil Rubbed Bronze
Reversible Medium Maple / Dark Maple Blades
with Acid Etched Glass
(Shown with Medium Maple Blades)

Shown with Cap for Non-Light Use

Iconic™



F672-ORB/AB

Oil Rubbed Bronze / Antique Brass Finish
Reversible Medium Maple / Dark Maple Blades
with Acid Etched Glass
(Shown with Dark Maple Blades)

Shown with Cap for Non-Light Use

Classic lines combined with advanced technology provide our traditional customers with a work horse that transcends time and will perform for many years to come. Die cast blade irons and face plate give a three-dimensional effect.



F672-MBK/BN

Matte Black / Brushed Nickel Finish
Reversible Medium Maple / Dark Maple Blades
with Acid Etched Glass
(Shown with Dark Maple Blades)

Shown with Cap for Non-Light Use

Great Room Traditional



F539-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades

Features:

- 14° Blade Pitch
- 72" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System
- Universal Light Kit Adaptable
(Sold Separately. See K9376-1 and
K9376-2 on page(s): 230)
- Quick Connect Switch Cup

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
9,071	106	85.36



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Great Room interiors require new ways to manage air. We have accomplished this with expanded blade spans, larger motors and enhanced housings in styles designed to complement those rooms.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F539-ORB

Oil Rubbed Bronze Finish
Dark Walnut Blades



F539-BN

Brushed Nickel Finish
Dark Walnut Blades

Santa Lucia™

minkaAire®
A Minka Group® Co.



F820-CT
Cattera Bronze™ Finish
Dark Walnut Blades
with Cognac Fluted Etched Glass



Features:

- 14° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System with Independent Up/Downlight Control
- Integrated Uplight
Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight
Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D556,882; D559,436; D568,984; D570,986; D574,948; D599,000; D599,466; 5,554,006
© 2006 Minka Lighting, Inc.

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,534	100	65.34



F820-IBR
Illuminati Bronze™ Finish
Dark Walnut Blades
with Silver Patina Glass



CM8222-IBR 22"
Illuminati Bronze™ Finish
22" Diameter
Matching Ceiling Medallion for F820-IBR
© 2005 Minka Lighting, Inc.



WCS212
Full Function Wall Control System Included
For Details See Page(s): 223

Lifetime WARRANTY

WallControl FULL FUNCTION



F812-10

Iron Oxide Finish
Dark Walnut Blades
with Venetian Scavo Glass

Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System
Independent Up/Downlight
- Integrated Uplight and Downlight
Uses 6-15W and 2-60W
Candelabra Bulbs (Included)
- Complements Lighting Available
Through Minka-Lavery®

U.S. Patent(s): D528,652; D531,298; D532,098;
D533,292; D535,012; D563,540

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,534	100	65.34



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Simple, clean, architectural lines
have been utilized to define
the Lineage™.



Salon Grand™



F707-FLP

Florence Patina™ Finish
Dark Walnut Blades
with Salon Scavo™ Glass

Inspired by Jessica McClintock's designs, the Salon Grand™ ceiling fan's exquisite styling, elegance and beauty exemplify her passion and love for romance.



JESSICA MCCLINTOCK HOME
The Romance Collection®
by
minkaAire
A Minka Group® Co.

Features:

- 14° Blade Pitch
- 56" 5 Blades
- 3½" and 10" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-50W Mini-Can Halogen
Bulbs (Included)
- Complements Lighting Available
Through Minka-Lavery®



U.S. Patent(s): D531,345; D532,152
© 2005 Minka Lighting, Inc.

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,825	97	70.16



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



CM1550-FLP 22"

Florence Patina™ Finish
22" Diameter
Matching Ceiling Medallion for F707-FLP
© 2005 Minka Lighting, Inc.





F900-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades

Shown with Optional **GC900 SET**
MADE WITH SPECTRA® CRYSTAL



F900-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades

Features:

- 14° Blade Pitch
- 68" 5 Blades
- 3½" and 16" Downrods
- Full Function Wall Control System with Independent Up/Downlight Control Feature
- Precision Machine Cut and Polished Lead-Free SPECTRA® CRYSTAL
- Integrated Uplight
Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight
Uses 2-50W Mini-Can Halogen Bulbs (Included)

© 2005 Minka Lighting, Inc.

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,022	95	63.39



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



Napoli™

minkaAire®
A Minka Group® Co.



F705-TSP

Tuscan Patina™ Finish
Tuscan Patina™ Shaded Blades
with Aged Champagne Glass



F705-STW

Sterling Walnut™ Finish
Sterling Walnut™ Shaded Blades
with Aged Champagne Glass

Features:

- 14° Blade Pitch
- 56" 5 Blades
- 3½" and 12" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-50W Mini-Can Halogen
Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690;
D516,702; D521,627; D522,122

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,765	93	72



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



CM7022-STW 22"

Sterling Walnut™ Finish
Matching Ceiling Medallion for F705/F715
© 2005 Minka Lighting, Inc.

Also Available:

CM7022-TSP 22"

Tuscan Patina™ Finish

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F715-STW

Sterling Walnut™ Finish
Sterling Walnut™ Shaded Blades
with Aged Champagne Glass



F715-TSP

Tuscan Patina™ Finish
Tuscan Patina™ Shaded Blades
with Aged Champagne Glass



CM7038-TSP 38"

Tuscan Patina™ Finish
Matching Ceiling Medallion for F705/F715
© 2005 Minka Lighting, Inc.

Also Available:

CM7038-STW 38"

Sterling Walnut™ Finish



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Features:

- 14° Blade Pitch
- 68" 5 Blades
- 3½" and 12" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-50W Mini-Can Halogen
Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690;
D516,702; D521,627; D522,122

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,581	104	72.84

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Volterra™ is a neo-classical inspiration,
incorporating an uplight with an integrated
halogen downlight.



F702-VB

Volterra Bronze™ Finish
Natural Walnut Blades
with French Scavo Glass

Volterra™



F702-BCW

Belcaro Walnut™ Finish
Natural Walnut Blades
with Aged Champagne Glass



Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Wall Control System
Independent Up/Downlight
- Integrated Uplight
Uses 6-15W Candelabra Bulbs
(Included)
- Integrated Halogen Downlight
Uses 2-50W Mini-Can Halogen
Bulbs (Included)

© 2002 Minka Lighting, Inc.

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,425	67	80.97



WCS213

Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl

Calais™



F544-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades
with Aged Champagne Glass

Elegance, style and performance for low ceiling applications, this fan has less than an 11-inch drop from ceiling to cap.

Features:

- 14° Blade Pitch
- 52" 5 Blades
- Flush Mount - Ideal for Low Ceilings
Less than 11" Drop from Ceiling
- Hand Held Remote Control System
- Integrated Light
Uses 2-60W Candelabra Bulbs (Included)

U.S. Patent(s): D526,714; D527,094; D530,415; D532,896; D536,777

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,050	80	75.63



F544-GBZ

Golden Bronze Finish
Dark Walnut Blades
with Excavation Glass



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222



Traditional Gyro™



A magnificent rendition of the original Gyro™ design, the traditional finish transcends the turns of time.

F502-PBL

Provençal Blanc Finish
Provençal Blanc Blades
Pearl White Glass

Features:

- High Performance Twin Turbofans Total Sweep 42"
- 20° Blade Pitch
- 4½" and 12" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)



F502-BCW

Belcaro Walnut™ Finish
Belcaro Walnut™ Blades
with Belcaro Walnut™ Glass



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51

U.S. Patent(s): D523,548; D523,549; D523,550; D523,983; D524,438; D526,059; D526,400; D526,712; D530,810; D532,097; D567,350; 6,832,902; 7,183,680; 7,229,255
© 2004 Minka Lighting, Inc.

Lifetime WARRANTY

WallControl FULL FUNCTION



Gyro Fans Rotate 360°

F802-KA

Kocoa Finish
Kocoa Blades
with Tinted Opal Glass

An addition to our popular Gyro™ family, the Vintage Gyro™ performs with the same efficiency and unsurpassed level of comfort as our other Gyro™ models, but with an early 20th Century style.


Vintage Gyro™



F802-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Gyro Fans Rotate 360°



F802-BN/CH

Brushed Nickel / Chrome Finish
Rosewood Blades
with Etched Opal Glass

Gyro Fans Rotate 360°



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Features:

- High Performance Twin Turbofans
Total Sweep 42"
- 20° Blade Pitch
- 3½" and 6" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360°
at 3 R.P.M.
- Full Function Wall Control System
Incorporating Fully Independent
Fan Head Speeds and Axis
Rotation
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F602-RRB

Restoration Bronze™ Finish
Restoration Bronze™ Blades
with Etched Opal School House Globe Glass

Gyro Fans Rotate 360°

Features:

- High Performance Twin Turbofans
Total Sweep 42"
- 3½" and 6" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360°
at 3 R.P.M.
- Full Function Wall Control System
Incorporating Fully Independent
Fan Head Speeds and Axis
Rotation
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,975; D489,443, D489,809;
D490,146; 6,832,902; 7,183,680; 7,229,255

Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

A truly unique design offering an unsurpassed level of comfort. The Gyro™ fan's ability to precisely control the direction and intensity of the cooling breeze efficiently circulates air in any environment.



Gyro Fans Rotate 360°

F602-BN/CH

Brushed Nickel / Chrome Finish
with Chrome Accents and Cages
Rosewood Blades
with Etched Opal Glass

Gyro™ Wet



F402-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Etched Opal School House Globe Glass

Gyro Fans Rotate 360°

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360°, and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

Features:

- High Performance Twin Turbofans Total Sweep 42"
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Galvanized Steel 3½" and 6" Downrods
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D478,975; D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255


Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



F402-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Gyro Fans Rotate 360°

Shown with Cap for Non-Light Use

Lifetime
WARRANTY

WallControl
FULL FUNCTION



For Wet Location

Gyrette™

minkaAire®
A Minka Group® Co.



F302-RRB

Restoration Bronze™ Finish
Restoration Bronze™ Blades

The Gyrette™ captures the design elements of the original Gyro™ in a smaller format. We have utilized flexible arms to maximize air circulation.

Features:

- High Performance Twin Turbofans
Total Sweep 36"
- Adjustable Turbofan Heads
- 14° Blade Pitch
- Complete Assembly Rotates 360°
at 3 R.P.M.
- 3-Speeds: 880, 1,120, 1,350
R.P.M.
- 30° Flexible Arms
- 4½" Downrod
- Full Function Hand Held Remote
Control System

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
2,418	53	45.62



Gyro Fans Rotate 360°



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

F302-BN

Brushed Nickel Finish
Brushed Nickel Blades

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

Indoor/Outdoor Collection



Minka-Aire® recognizes a need in today's al fresco lifestyle by offering an Outdoor Series of ceiling fans. All are UL or ETL Listed for wet location usage, making these fans perfect for patios, porches, and other exposed areas. Motor housings and blades are fully protected against water and all weather conditions. Particular models have a combined waterproof light kit to provide additional lighting outdoors. These fans feature various designer finishes to complement your patio furniture.

Now you are able to enjoy a wonderful breeze on your patio, in your gazebo or over your outdoor spa! Of course, you may use all of these models indoors as well.

Concept™ I Wet 58"

STAINLESS STEEL



F477-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Pietra Glass


Features:

- 14° Blade Pitch
- 58" 3 Blades
- Marine Grade Stainless Steel Construction
- Stainless Steel 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;
D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,400	64	115



F477-WH

White Finish
White Blades
with White Opal Glass

Shown with Cap for Non-Light Use

Lifetime
WARRANTY

WallControl
FULL FUNCTION



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



For Wet Location



STAINLESS STEEL

F477-BNW

Brushed Nickel Wet Finish
Silver Blades
with White Opal Glass

Shown with Cap for Non-Light Use

STAINLESS STEEL

UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series. Concept™ I Wet is constructed of marine grade stainless steel to ensure long lasting appearance and function in the toughest environments.

STAINLESS STEEL

Concept™ I Wet 52"



F577-BNW

Brushed Nickel Wet Finish
Silver Blades
with White Opal Glass

Features:

- 14° Blade Pitch
- 52" 3 Blades
- Galvanized Steel
3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;
D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,991	51.2	117.01

The Concept™ I ceiling fan collection is the most successful series in the history of Minka-Aire®. It is only natural that we would produce a new version that is UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series.

Lifetime
WARRANTY

WallControl
FULL FUNCTION

UL
LISTED
For Wet Location



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223



F476-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with Pietra Glass



F476-WH

White Finish
White Blades
with White Opal Glass

Shown with Cap for Non-Light Use

Sunseeker

F532-BWH

Bone White Finish
Bone White Blades

Features:

- 14° Blade Pitch
- 60" 5 Blades
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- 3-Speed Pull Chain
- Indoor/Outdoor Use
UL Listed for Wet Locations
- UL Wet Location Light Kits
Available
(Sold Separately. Page(s): 231)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,783	65	104.19

Lifetime
WARRANTY

UL
LISTED
For Wet Location



The Sunseeker features a 60-inch blade span, stylish transitional design and superb value. These elements make it an ideal choice for enjoying hot summer days outdoors.




F532-BNW

Brushed Nickel Wet Finish
Silver Blades



F532-DRF

Driftwood Finish
Driftwood Blades



F532-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades




F840-CF

Craftsman™ Finish
Craftsman™ Blades
with Craftsman™ Glass

Features:

- 14° Blade Pitch
- 52" 5 Blades
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Full Function Wall Control System
- Light Kit with Enclosed Glass
Shades
Uses 3-60W Candelabra Bulbs
(Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)



F840-CF

Shown with Cap for
Non-Light Use

U.S. Patent(s): D579,097; D579,098; D579,103;
D581,512; D583,044

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,374	77.7	69.16



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Inspired by the Craftsman architecture of the early 1900s, this fan best defines the spirit of the era. It can be used in both interior and exterior applications.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



For Wet Location





F580-VR/BB

Vintage Rust™ Finish
Bamboo All Weather Blades
Shown with Cap for Non-Light Use

Our wicker design, coupled with a Vintage Rust™ finish, replicates a highly popular tropical motif.

Features:

- 14° Blade Pitch
- 52" 5 Blades
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- 3-Speed Pull Chain
- Snap Lock/Set Screw Blade Assembly System
- Integrated Halogen Caged Etched Glass Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Location
- Cap for Non-Light Use (Included)

U.S. Patent(s): D501,251; D501,922; D501,923; D502,770; D508,287; D514,215; D522,643; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,375	79	68.03



F580-VR/BB

Vintage Rust™ Finish
Bamboo All Weather Blades
with Caged Etched Glass

Lifetime
WARRANTY



For Wet Location





F582-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with Vintage Amber Glass



F582-BNW

Brushed Nickel Wet Finish
Silver Blades
with Acid Etched Glass

Rainman™



F582-GL

Galvanized Finish
Silver Blades
with Acid Etched Glass

Reminiscent of lighting often found along shoreline walkways, the Rainman™, as the name suggests, is an excellent choice for exterior as well as interior use.

Features:

- 14° Blade Pitch
- 54" 5 Blades
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- Wall Control System
- Integrated Halogen Caged Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations

U.S. Patent(s): D460,549

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,508	58	94.96



WCS213

Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl



LISTED
For Wet Location


www.minkaaire.com

131

Slipstream XXL



Slipstream XXL is the second generation of our uniquely designed 8 blade, 65-inch fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and a form with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.



F889-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Features:

- 14° Blade Pitch
- 84" 8 Concave Blades
- DC 165 x 25mm Motor
- Galvanized Steel 3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- Special Hand Held Remote Control System Included - RC400
- Integrated Light Uses 1-26W Non-Dimmable GU24 CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations

Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27



Slipstream XXL



Slipstream XXL is the second generation of our uniquely designed 8 blade, 65-inch fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and a form with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.



F889-SI

Smoked Iron Finish
Smoked Iron Blades
with Etched Opal Glass



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Features:

- 14° Blade Pitch
- 84" 8 Concave Blades
- DC 165 x 25mm Motor
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Special Hand Held Remote Control
System Included - RC400
- Integrated Light
Uses 1-26W Non-Dimmable GU24
CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations

Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27



Slipstream XXL



Slipstream XXL is the second generation of our uniquely designed 8 blade, 65-inch fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and a form with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.



F889-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Shown with Cap for Non-Light Use

Features:

- 14° Blade Pitch
- 84" 8 Concave Blades
- DC 165 x 25mm Motor
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Special Hand Held Remote Control
System Included - RC400
- Integrated Light
Uses 1-26W Non-Dimmable GU24
CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27

U.S. Patent(s): D715,917



Strata



F734-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Features:

- 12° Blade Pitch
- 52" 4 Blades
- Galvanized Steel
3½" and 6" Downrods
(Uses ¾" I.D. DR5 Series Downrod)
- Hand Held Remote Control System
- Integrated Light
Uses 1-75W Mini-Can Halogen
Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,098	47.6	107



F734-ORB

Shown with Cap for
Non-Light Use

The Strata with its Smoked Iron or Galvanized finishes adds a rustic yet contemporary style to your home.

Lifetime
WARRANTY

Remote
CONTROL



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222



LISTED

For Wet Location





F734-GL

Galvanized Finish
Silver Blades
with Etched Opal Glass



F734-GL

Shown with Cap for
Non-Light Use



F734-SI

Smoked Iron Finish
Smoked Iron Blades
with Etched Opal Glass



F579-L-BNW

Brushed Nickel Wet Finish
Silver Blades
with Frosted Seeded Glass



F579-L-BNW

Shown with Cap for
Non-Light Use

Magellan®

F579-L-ORB

Oil Rubbed Bronze Finish
Parchment Blades
with Vintage Amber Seeded Glass

Features:

- 16° Blade Pitch
- 60" 5 Sail Blades
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D446,296; D449,372; D449,682;
D449,683; D450,832

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,343	65	82.20

F579-L-ORB

Shown with Cap for
Non-Light Use



WCS213

Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl



For Wet Location

www.minkaaire.com

141

Aluma Wet



F523-ABD

Brushed Aluminum Finish
Silver Blades
with Etched Opal Glass

Shown with Cap for Non-Light Use

Features:

- 12° Blade Pitch
- 52" 4 Blades
- 3½" and 6" Downrods
- All Aluminum Construction
- Hand Held Remote Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,988	52	96



F523-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222

Lifetime
WARRANTY

Remote
CONTROL



LISTED

For Wet Location





F523-WHF

Flat White Finish
Flat White Blades
with Etched Opal Glass

Aluma Wet is our answer to the fan that goes anywhere and has everything. For use indoors and outdoors, Aluma Wet is UL listed for use in wet locations. Produced from weather resistant materials, the Aluma Wet provides air circulation for every location including patio, porch and pergola.

Java



F753-KA

Kocoa Finish
Kocoa Blades

Features:

- 14° Blade Pitch
- 54" 3 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Indoor/Outdoor Use
UL Listed for Wet Locations

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,681	60	94

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.

Lifetime
WARRANTY

Remote
CONTROL



LISTED
For Wet Location



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222



□ **F753-WHF**

Flat White Finish
Flat White Blades



□ **F753-BNW**

Brushed Nickel Wet Finish
Silver Blades



F474-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with Pietra Glass



F474-WH

White Finish
White Blades
with White Opal Glass
Shown with Cap for Non-Light Use

Concept™ II Wet



F574-BNW

Brushed Nickel Wet Finish
Silver Blades
with White Opal Glass

As the name implies, the Concept™ II Wet ceiling fan is “a taste of things to come.” Simple in style, yet ingenious by design and UL Listed for wet locations.

Features:

- 14° Blade Pitch
- 52" 3 Concave Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 12"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
(Will Not Pendulum In Windy Conditions)



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,053	51.3	117.99

U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192



UL LISTED
For Wet Location

Lifetime WARRANTY

WallControl FULL FUNCTION

Traditional Concept™ 52"



F594-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass

Features:

- 14° Blade Pitch
- 52" 3 Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 10 3/4"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,565	61	108.52

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl
FULL FUNCTION



LISTED
For Wet Location





F594-PW

Pewter Finish
Dark Maple Blades
with Opal Glass



F594-WH

White Finish
White Blades
with Opal Glass

Traditional Concept™ 44"



Features:

- 14° Blade Pitch
- 44" 3 Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 10 3/4"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,940	49	100

F593-PW

Pewter Finish
Dark Maple Blades
with Opal Glass

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl
FULL FUNCTION



LISTED
For Wet Location





F593-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass



F593-WH

White Finish
White Blades
with Opal Glass

Shown with Cap for Non-Light Use

Terrana



Features:

- 16° Blade Pitch
- 52" 2 or 3 Blades (Included)
- 2 Sets of Blade Irons (For Each Configuration)
- Galvanized Steel 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Integrated Light Uses 1-75W Mini Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

F680-KA

Kocoa Finish
Palm / Rattan Reversible Blades
with Tinted Opal Glass



2-Blade Option Shown with Rattan Blades and Cap for Non-Light Use

2 Blade Energy Information

(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,439	52	85.7

3 Blade Energy Information

(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,155	52.5	79



2-Blade Option Shown with Palm Blades with Tinted Opal Glass



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Lifetime WARRANTY

Remote CONTROL FULL FUNCTION



LISTED For Wet Location





F680-BG


Bahama Beige™ Finish
Palm / Rattan Reversible Blades
with Tinted Opal Glass

With its 2 or 3-blade configurations and reversible blade styles, the Terrana evokes a sense of tropical breezes in any setting. Unique options and superb functionality are paramount in the Terrana.



Eight Different Configurations all in One Box. Includes Palm/Rattan Reversible Blades.

2-Blade Option Shown with Rattan Blades and Cap for Non-Light Use



3-Blade Option Shown with Palm Blades and Cap for Non-Light Use

Gauguin™



F581-BG

Bahama Beige™ Finish
Bahama Beige™ Blade
with Etched Glass

Features:

- 14° Blade Pitch
- 52" 4 Blades
- Galvanized Steel
3½" and 6" Downrods
(Uses ¾" I.D. DR5 Series Downrod)
- Stainless Steel Hardware and
All Weather Blades
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-50W MR16 120V 2-Pin
Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D513,319; D514,691; D514,692;
D516,703; D517,201; D519,199

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,834	52	92.97

Lifetime
WARRANTY

WallControl
FULL FUNCTION



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Tropical style influences the Gauguin™ by incorporating a remarkable combination of performance and unique design elements.



LISTED

For Wet Location





F581-WHF

Flat White Finish
Flat White Blades
with Etched Glass



F581-ORB

Oil Rubbed Bronze Finish
Bahama Beige™ Blades
with Etched Glass

Sundowner®

F589-ORB

Oil Rubbed Bronze Finish
Dark Maple Blades

Features:

- 16° Blade Pitch
- 54" 5 Blades
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- 3-Speed Pull Chain
- Poly Molded and ABS Components
- Indoor/Outdoor Use
UL Listed for Wet Locations
- UL Wet Location Light Kits
Available
(Sold Separately. Page(s): 231)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,523	79	82

Lifetime
WARRANTY



Accessory Blades Available. See Page(s): 236

Highly recommended for the most challenging environments, the Sundowner® combines superior performance with weatherproof components designed to withstand all outdoor conditions.

F589-BWH

Bone White Finish
Bone White Blades



F589-SWH

Shell White Finish
Shell White Blades



F589-DRF

Driftwood Finish
Driftwood Blades



F589-MW

Mossoro Walnut™ Finish
Mossoro Walnut™ Blades

Sundowner®



F589-HT

Heritage™ Finish
Black Blades

Features:

- 16° Blade Pitch
- 54" 5 Blades
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- 3-Speed Pull Chain
- Poly Molded and ABS Components
- Indoor/Outdoor Use
UL Listed for Wet Locations
- UL Wet Location Light Kits
Available
(Sold Separately. Page(s): 231)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,523	79	82



F589-WH

White Finish
White Blades

Lifetime
WARRANTY


LISTED
For Wet Location



Accessory Blades Available. See Page(s): 236



F589-VRT

Vintage Rust™ Finish
Dark Maple Blades



F589-BI/AI

Black Iron with Aged Iron Accents Finish
Black Iron Blades



□ **F571-DRF 52"**

Driftwood Finish
Gray Blades



□ **F571-WH 52"**

White Finish
White Blades



□ **F571-ORB 52"**

Oil Rubbed Bronze Finish
Dark Oak Finish Blades

Sundance™



F572-WH 42"

White Finish
White Blades

Perfect for the porch, patio, gazebo or courtyard, the Sundance™ was designed to withstand all of the elements.

Features:

- 12° Blade Pitch
- 52" or 42" 5 Blades
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- 3-Speed Pull Chain
- Indoor/Outdoor Use
UL Listed for Wet Locations
- UL Wet Location Light Kits Available
(Sold Separately. Page(s): 231)

F571 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,596	63	88.4

F572 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,428	52	65.64



F572-ORB 42"

Oil Rubbed Bronze Finish
Dark Oak Finish Blades



Gyro™ Wet

F402-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Etched Opal School House Globe Glass

Gyro Fans Rotate 360°

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360°, and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

Features:

- High Performance Twin Turbofans Total Sweep 42"
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Galvanized Steel 3½" and 6" Downrods
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,975; D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51

Lifetime WARRANTY

WallControl FULL FUNCTION



LISTED For Wet Location



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Gyro Fans Rotate 360°

F402-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Shown with Cap for Non-Light Use



F1000-BN

□ Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Finish Blades
with Etched Lens
(Shown with Dark Walnut Blades)

Value Collection

With the Minka-Aire® Value Collection, one need not sacrifice style and performance for affordability.

Choose from several finishes and light kit options to find the right Minka-Aire® ceiling fan with timeless style and design for the budget-conscious customer.

Dyno

with LED Light

LED

LED

F1000-BN

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Finish Blades
with Etched Lens
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Integrated Light
Uses 17W Dimmable LED
(Included) 3 Year Warranty
- 1100 Lumens
- 2700K
- CRI 80
- Hand Held Remote Control System
- Replacement LED Assembly
(Part #6F1000LK01)

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,295	64	77



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222

A new addition to our Value Collection, featuring performance and design features at an affordable price. For the first time in our Value offerings, we introduce a fan with an integrated LED* light source. Generous in size, style, adaptability and function, Dyno becomes one of our core fan offerings.

LED



LED



F1000-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Finish Blades
with Etched Lens
(Shown with Dark Walnut Blades)

LED



F1000-WH

White Finish
White Finish Blades
with Etched Lens

Traditional Mojo



F622-BWH

Bone White Finish
Bone White Blades
with Bone White Glass

The Traditional Mojo is the next generation of our highly successful Mojo series. Traditional accents integrate perfectly for your home.



F622-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Etched White Glass
(Shown with Medium Maple Blades)



F622-ORB/TS

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Medium Maple Blades)



F622-PW

Pewter Finish
Reversible Medium Maple / Dark Walnut Blades
with Etched White Glass
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrod
- 3-Speed Pull Chain
- Low Profile Bowl Light Kit
Uses 3-60W Candelabra Bulbs
(Included)
- Cap for Non-Light Use (Included)
- Solid Cap and Finial Included for
Adaptation for Remote Control Use

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,699	66.1	86.22

Lifetime
WARRANTY

Mojo



F522-ORB/TS

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Medium Maple Blades)

Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Low Profile Light Kit
Uses 3-60W Candelabra Bulbs
(Included)
- Warp Resistant Plywood Blades
- Cap for Non-Light Use (Included)
- Solid Cap and Finial Included for
Adaptation for Remote Control Use

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,295	65.7	81



F522-BN

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Medium Maple Blades)

Lifetime
WARRANTY



F522-WH

White Finish
White Blades
with Frosted White Glass



F522-BWH

Bone White Finish
Bone White Blades
with Frosted White Glass



F522-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Medium Maple Blades)

Mojo II



□ **F533-BN**

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Dark Walnut Blades)



□ **F533-DK**

Distressed Koa Finish
Reversible Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Dark Walnut Blades)



□ **F533-WH**


White Finish
White Blades
with Frosted White Glass



F533-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Dark Walnut Blades)

The Mojo II is the newest addition to our Value Collection featuring a wealth of performance and an integrated light source. A great value for low ceiling applications.



F533-BWH

Bone White Finish
Bone White Blades
with Bone White Glass

Features:

- 14° Blade Pitch
- 52" 4 Blades
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 13" with Light
- 3-Speed Pull Chain
- Integrated Downlight
Uses 3-60W Candelabra Bulbs (Included)
- Solid Cap and Finial Included for Adaptation for Remote Control Use

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,138	62.6	82



Hilo



F470-BN

Brushed Nickel Finish
Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrod
- 3-Speed Pull Chain
- Reversible Warp Resistant Blades
- Bowl Light Kit
Uses 3-40W Candelabra Bulbs
(Included)
- Cap for Non- Light Use

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,828	64.7	74.62

The Hilo's clean lines provide elegance and simplicity suitable for a variety of environments.

Lifetime
WARRANTY



F470-WH

White Finish
White / Medium Maple Blades
with Frosted White Glass
(Shown with White Blades)



F470-ORB

Oil Rubbed Bronze Finish
Medium Walnut / Dark Walnut Blades
with Tea Stain Glass
(Shown with Medium Maple)

Bolo™



Four of our best selling finishes accent this fan, creating a decorative alternative to an everyday need. Includes glass bowl light kit and remote control system.

F620-BN

Brushed Nickel Finish
Dark Walnut Blades
with Etched Swirl Glass

Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Bowl Light Kit
Uses 3-60W Candelabra Bulbs
(Included)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,712	74	77.19



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222



F620-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Excavation Glass





F620-DBB

□ Dark Brushed Bronze Finish
Dark Maple Blades
with Avorio Mezzo™ Glass



F620-BCW

□ Belcaro Walnut™ Finish
Dark Walnut Blades
with Excavation Glass



F614-DBB

Dark Brushed Bronze Finish
Dark Maple Blades

Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 229)
- Custom Light Kit K9614 Available
(Sold Separately. Page(s): 235)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,257	70.5	89

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.



Timeless



F614-MCG

Mottled Copper with Gold Highlights Finish
Dark Walnut Blades



F614-PI

Patina Iron Finish
Dark Maple Blades



F614-PW

Pewter Finish
Dark Walnut Blades

Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- Custom Light Kit K9614 Available (Sold Separately. Page(s): 235)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,257	70.5	89



F614-FB

French Beige Finish
Medium Maple Blades



Timeless

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.



F614-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



F689-KA

Kocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)

The Kola-XL 60-inch fan features the same design elements as the Kola 52-inch. It has been upgraded to provide the performance necessary for larger rooms and has the convenience of an electronic control system.



F689-PW

Pewter Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Maple Blades)

Kola-XL



F689-WH

White Finish
White Blades



F689-DBB

Dark Brushed Bronze Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,557	84.6	89



Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222





F688-PW

Pewter Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Maple Blades)

Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 229)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,002	71.3	84



F688-KA

Cocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)




Kola



F688-WH

White Finish
White Blades

Smooth lines with a sleek blade iron design and a robust body make the Kola a perfect complement to any home decor.



F688-DBB

Dark Brushed Bronze Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Walnut Blades)



F696-CC

□ Cognac Finish
Reversible Natural Walnut / Dark Walnut Blades
(Shown with Natural Walnut Blades)



F696-KA

□ Cocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)

Kafé-XL



F696-WH

White Finish
White Blades

Simple elegance defined in rich new finishes, the Kafé-XL brings an exciting new look with enhanced features to our value collection.



F696-VP

Vineyard Patina Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Walnut Blades)



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222

Features:

- 12° Blade Pitch
- 60" 5 Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,557	84.6	89

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION





F695-KA

Kocoo Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)

Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 229)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,002	71.3	84

Simple yet elegant in several finishes, the Kafé brings a refreshing new look to our value collection.



Kafé



F695-CC

Cognac Finish
Reversible Natural Walnut / Dark Walnut Blades
(Shown with Natural Walnut Blades)



F695-WH

White Finish
White Blades



F695-VP

Vineyard Patina Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Maple Blades)

Classica



F759-PBL Gallery Edition

Provencal Blanc Finish
Provencal Blanc Blades
with Etched Glass

Includes:
Integrated 3-Light Kit
Uses 3-60W Candelabra Bulbs
(Included)
Hand Held Remote Control System

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 229)
- Custom Light Kit K9659 Available
(Sold Separately. Page(s): 235)

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.

© 2009 Minka Lighting, Inc.

Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,313	71.6	88

Lifetime
WARRANTY



F659-PBL

Provencal Blanc Finish
Provencal Blanc Blades






F659-BCW
Belcaro Walnut™ Finish
Dark Walnut Blades



F659-FB
French Beige Finish
Medium Maple Blades



F659-DRF
Driftwood Finish
Driftwood Blades



F659-PI
Patina Iron Finish
Dark Walnut Blades



F588-SP-WH

White Finish
White Blades

Ultra-Max™, by name and performance, is engineered with a 14° blade pitch to provide maximum comfort in even the largest areas. Its clean, traditional styling will be “right at home” in any setting.



F588-SP-BN


Brushed Nickel Finish
Dark Walnut Blades

Ultra-Max™



F588-SP-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades



F588-SP-BWH

Bone White Finish
Bone White Blades

Features:

- 14° Blade Pitch
- 54" 5 Blades
- 3½" and 6" Downrods
- Full Function Wall Control System and Hand Held Remote Control
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,341	76.4	83



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 222



WCS212

Full Function Wall Control System Included
For Details See Page(s): 223

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Remote
CONTROL
FULL FUNCTION



F569-BS

Brushed Steel Finish
Silver Blades
with Opal Glass

A truly exceptional value! All the benefits of the Supra® 52" packaged with additional bells and whistles including a matching light kit and RCS223 Remote Control System.

F569-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Opal Glass

Supra[®] 52"

with Light Kit
and Remote Control System



F569-BS/DW

Brushed Steel Finish
Dark Walnut Blades
with Opal Glass



F569-WH

White Finish
White Blades
with Opal Glass



RCS223

Hand Held Remote Control Included
For Details See Page(s): 222

Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Halogen Light Kit
Uses 1-100W Mini-Can Halogen Bulb (Included)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,755	79	72.85

Lifetime
WARRANTY

Remote
CONTROL

The Supra® 52" offers decorative versatility in multiple finishes. It has clean, modern styling and uncompromising quality with superior performance.

Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,995.05	75.3	79.62




Accessory Blades Available. See Page(s): 236



F568-KA

Kocoa Finish
Reversible Toned Medium Maple / Medium Maple Blades
(Shown with Toned Medium Maple Blades)




F568-BWH

Bone White Finish
Bone White Blades

Supra[®] 52"



F568-SWH
Shell White Finish
Shell White Blades



F568-BS/DW
Brushed Steel Finish
Dark Walnut Blades



□ **F568-WH**

White Finish
White Blades



□ **F568-BCW**

Belcaro Walnut™ Finish
Dark Walnut Blades

Supra[®] 52"



F568-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



F568-BS

Brushed Steel Finish
Silver Blades

Features:

- 14° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,995.05	75.3	79.62

Lifetime
WARRANTY



Accessory Blades Available. See Page(s): 236



F563-SP

- Brushed Steel Finish
Silver Blades
with Opal Glass



F563-SP-BS/DW

- Brushed Steel Finish
Dark Walnut Blades
with Opal Glass

Supra[®] 44"

with Light Kit



F563-SP-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Opal Glass

The Supra[®] 44", model F563-SP is a great economical option, packaged with a light kit to meet every need.



F563-SP-WH

White Finish
White Blades
with Opal Glass

Features:

- 14° Blade Pitch
- 44" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Halogen Light Kit
Uses 1-100W Mini-Can Halogen Bulb (Included)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,272	76	69.37

Lifetime
WARRANTY

Supra[®] 44"



F563-BS/DW

Brushed Steel Finish
Dark Walnut Blades

Designed with superior performance and all of the features found in full-size fans made available for mid-size rooms.

Features:

- 14° Blade Pitch
- 44" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,272	76	69.37

F563-BS

Brushed Steel Finish
Silver Blades



Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 236



F563-ORB
Oil Rubbed Bronze Finish
Medium Maple Blades



F563-WH
White Finish
White Blades

Supra[®] 32"



F562-WH

White Finish
White Blades

Features:

- 22° Blade Pitch
- 32" 6 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)
- 6-Ply Warp Resistant Blades

U.S. Patent(s): D450,830

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,075	66	61.73

Fashion, form and function for the smallest areas are highlighted in the Supra[®] 32". The perfect choice for bathrooms, hallways, entries and walk-in closets.

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 236




F562-BS

Brushed Steel Finish
Silver Blades



F562-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



F556L-BN

Brushed Nickel Finish
Silver Blades
with Etched Lens

LED

Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Uses 17W LED (Included)
3 Year Warranty
- 1100 Lumens
- 3000K
- CRI 80
- Replacements LED Assembly
(Part #6F1000LK01)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,966	66.5	89.71



F556L-BWH

Bone White Finish
Bone White Blades
with Etched Lens

LED



RCS213

Hand Held Remote Control Included
For Details See Page(s): 222



Contractor LED

LED

F556L-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Etched Lens
(Shown with Medium Maple Blades)

Smart simplicity at its best. This contractor LED provides greater performance and offers energy efficiency through the use of the latest LED technology.

LED

F556L-BN/DW

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
with Etched Lens
(Shown with Dark Walnut Blades)



F556-BN

Brushed Nickel Finish
Silver Blades



F556-BWH

Bone White Finish
Bone White Blades

Features:

- 12° Blade Pitch
- 52" 5 Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,966	66.5	89.71



Contractor Plus



F556-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
(Shown with Medium Maple Blades)

Our new Contractor Plus fan continues our tradition of offering design and reliability in several finishes.



F556-BN/DW

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
(Shown with Dark Walnut Blades)

Contractor Uni-Pack

with 3-Light Kit

F647-BS

Brushed Steel Finish
Dark Walnut Blades
with Etched Glass


Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Integrated Light Kit
Uses 3-60W Candelabra Bulbs
(Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,901	62	79.05

Offering affordable performance and reliability with designer finishes, the Contractor fan now comes with an integrated light kit.



F647-SWH

Shell White Finish
Shell White Blades
with Etched Glass

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 236



F647-ORB/TS

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tea Stain Glass



F647-WH

White Finish
White Blades
with Etched Glass



F647-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Etched Glass

Contractor Uni-Pack

with Bowl Light Kit



F648-BS

Brushed Steel Finish
Dark Walnut Blades
with Etched Swirl Glass

Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)
Uses 2-13W Non-Dimmable GU24
Spiral CFL Bulbs (Included)
- Pre-Installed One-Piece Motor
Blade Iron Gasket
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,408	65	82.69

Our most economical and efficient fan and light combination for the budget-conscious customer, helping to save money and protect the environment through energy efficient products.

Lifetime
WARRANTY



Accessory Blades Available. See Page(s): 236



F648-ORB/EX
Oil Rubbed Bronze Finish
Medium Maple Blades
with Excavation Glass



F648-WH
White Finish
White Blades
with Etched Swirl Glass



F648-ORB
Oil Rubbed Bronze Finish
Medium Maple Blades
with Etched Swirl Glass



F548-WH

White Finish
White Blades
with Etched Swirl Glass



F548-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Etched Swirl Glass

Contractor Uni-Pack

with Bowl Light Kit



F548-ORB/EX

Oil Rubbed Bronze Finish
Medium Maple Blades
with Excavation Glass

Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)
Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,636	64	73.01


The most economical and efficient fan and light combination for the secondary rooms in the house.

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 236

www.minkaaire.com

213



□ **F548-BS**

Brushed Steel Finish
Silver Blades
with Etched Swirl Glass



□ **F548-BWH**

Bone White Finish
Bone white Blades
with Etched Swirl Glass

Contractor Uni-Pack

with Bowl Light Kit



F548-BS/DW

Brushed Steel Finish
Dark Walnut Blades
with Etched Swirl Glass

Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)
Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor
Blade Iron Gasket
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,636	64	73.01

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 236

www.minkaaire.com

215

Contractor 52"



F547-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades

Features:

- 12° Blade Pitch
- 52" 4 or 5 Blades
- 4" Downrod
(Uses 3/4" I.D. DR5 Series Downrod)
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Pre-Installed One-Piece Motor/
Blade Iron Gasket
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 229)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,565.39	61	74.84

Our Contractor series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demands.



F547-ABR

Antique Bronze Finish
Medium Maple Blades

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 236



F547-BS/DW

Brushed Steel Finish
Dark Walnut Blades



F547-BWH

Bone White Finish
Bone White Blades



F547-WH

White Finish
White Blades



F547-BS

Brushed Steel Finish
Silver Blades



F546-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



F546-BS

Brushed Steel Finish
Silver Blades

Contractor 42"



F546-BS/DW

Brushed Steel Finish
Dark Walnut Blades

Our Contractor 42" series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demand.



F546-WH

White Finish
White Blades

Features:

- 12° Blade Pitch
- 42" 5 Blades
- 4" Downrod
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Pre-Installed One-Piece Motor/ Blade Iron Gasket
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,290	47	70.01

Lifetime
WARRANTY

Mesa

minkaAire®
A Minka Group® Co.



F565-WH 52"

White Finish
White Blades

Our close-to-ceiling economy model in two sizes will move air in the tightest places.

Features:

- 12° Blade Pitch
- 52" or 42" 5-Blades
- Flush Mount 8¾" Overall Ceiling Drop
- 3-Speed Pull Chain
- One-Piece Stamped Body
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 229)

F565 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,092	65	78

F566 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,291	50	65.82



F566-WH 42"

White Finish
White Blades

Lifetime
WARRANTY

Finishes



ABD
Brushed Aluminum



ABR
Antique Bronze



BCW
Belcaro Walnut™



BG
Bahama Beige™



BI/AI
Black Iron/
Aged Iron Accents



BK
Black



BN
Brushed Nickel
(Plated)



BNW
Brushed Nickel Wet
(Plated)



BS
Brushed Steel



BWH
Bone White



CC
Cognac



CF
Craftsman™



CH
Chrome
(Plated)



CPBR
Copper Bronze



CT
Cattera Bronze™



DBB
Dark Brushed Bronze



DK
Distressed Koa



DKG
Distressed Koa
with Gold Highlights



DRB
Dark Restoration Bronze™



DRF
Driftwood



FB
French Beige



FLP
Florence Patina™



GBZ
Golden Bronze



GM
Gun Metal



GL
Galvanized



HT
Heritage™



IBR
Illuminati Bronze™



IO
Iron Oxide



KA
Kocoo



LN
Liquid Nickel
(Plated)



MCG
Mottled Copper
with Gold Highlights



MG
Mahogany



MP
Maple



MW
Mossoro Walnut™



ORB
Oil Rubbed Bronze



PBL
Provencal Blanc



PI
Patina Iron



PN
Polished Nickel
(Plated)



PW
Pewter



RD
Red



RRB
Restoration Bronze™



RW
Rosewood



SI
Smoked Iron



SL
Silver



STW
Sterling Walnut™



SWH
Shell White



TB
Toned Brass
(Plated)



TSP
Tuscan Patina™



VB
Volterra Bronze™



VP
Vineyard Patina



VRT
Vintage Rust™



WH
White



WHF
Flat White

Hand-painted finishes and components made from natural material may reflect variations in color and texture. These are not imperfections and enhance the unique appearance of each and every Minka-Aire® fixture. Specifications are subject to change at any time.

Control Systems



RCS212 - 256 Bit

RCS212 Full Function Hand Held AireControl® Remote System

- Three Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer with Independent Up/Downlight Control
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS212 Wall Mount AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RCS213 - 256 Bit

RCS213 Hand Held AireControl® Remote System

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS223 Wall AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RCS223 - 256 Bit

RCS223 Hand Held AireControl® Remote System

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster and Canopy Mounted Receiver
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS213 Wall AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RC400 / RC500 / RC600

RC400 AireControl® Remote System

- For F726, F823, F828, F887 and F888 Fans Only
- Six Speed Fan Control in Forward and Reverse
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In

U.S. Patent(s): D533,514; D551,008

RC500 AireControl® Remote System

- For F737 and F853 Fans Only
- Same Features as RC400 AireControl® System

U.S. Patent(s): D533,514; D551,008

RC600 AireControl® Remote System

- For F617, F745 and F905 Fans Only
- Same Features as RC400 AireControl® System

U.S. Patent(s): D533,514; D551,008



Full Function Hand Held Remote Control



An ultra-thin design exclusive to Minka-Aire®, the remote enables the user with one finger to control all functions of Minka-Aire® ceiling fans.

AireControl® by Minka-Aire® controls all functions: reverse, uplight (where applicable), fan light, speed control, as well as off-on. (RCS212 and WCS212)

RCS213, RCS223, WCS213 and WCS223 controls do not include the reverse function.

Included is a holster if you want to wall mount the control for your convenience.

Please Note:

256 Bit remote systems are not compatible with 32 Bit remote systems.

**WC105-WH
Speed Control**

- Four Speed Fan Control
- 2-Wire Installation



WC105-WH White

**WC106-WH
Speed Control**

- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



WC106-WH White

**WC110
Speed Control**

- For F510 Fans Only
- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



WC110

**WCS212
Full Function AireControl®**

- Same Features as RC212 Hand Held
- Includes Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS212 - 256 Bit

**WCS213
AireControl®**

- Same Features as RCS213 Hand Held
- Includes Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS213 - 256 Bit

**WCS223
AireControl®**

- Same Features as RCS223 Hand Held
- Includes Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS223 - 256 Bit

Please Note:

256 Bit remote systems are not compatible with 32 Bit remote systems.

Control Systems

Fan Control Systems Compatibility Chart

Fan Model	Fan Name	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F302	Gyrette™	120	Incl.					•		
F402	Gyro™ Wet	119, 162	•					Incl.		
F470	Hilo	172-173		•	•		•		•	•
F474	Concept™ II Wet	146-147	•					Incl.		
F476	Concept™ I Wet	124-125	•					Incl.		
F477	Concept I Wet 58"	122-123	•					Incl.		
F502	Traditional Gyro™	115	•					Incl.		
F510	Spacesaver	90-91				Wall Control Included WC110				
F513	New Era	92-93	Incl.					•		
F514	Zen	82-83	Incl.					•		
F516	Concept™ I 44"	66-67	Incl.					•		
F517	Concept™ I 52"	66-67	Incl.					•		
F518	Concept™ II 44"	64-65	Incl.					•		
F519	Concept™ II 52"	62-63	Incl.					•		
F521	Aluma	70-71		•	•		Incl.		•	•
F522	Mojo	168-169		•	•				•	•
F523	Aluma Wet	142-143		Incl.						
F524	Roto	54-55			•	Incl.				•
F528	San Francisco®	74		•			•		Incl.	
F529	San Francisco®	74-75		•			•		Incl.	
F531	Flyte®	72-73		•			•		Incl.	
F532	Sunseeker	126-127				•	•			
F539	Great Room Traditional	104-105	•					Incl.		
F544	Calais™	114		Incl.			•		•	
F546	Contractor 42"	218-219		•	•	•	•		•	•
F547	Contractor 52"	216-217		•	•	•	•		•	•
F548	Contractor Uni-Pack	208-215		•	•		•		•	•
F556L	Contractor LED	204-205		Incl.					•	
F562	Supra® 32"	202-203		•	•	•	•		•	•
F563	Supra® 44"	200-201		•	•	•	•		•	•
F563	Supra® 44" -SP	198-199		•	•	•	•		•	•
F565	Mesa™ 52"	220				•	•			
F566	Mesa™ 42"	220				•	•			
F568	Supra® 52"	194-197		•	•	•	•		•	•
F569	Supra® 52"	192-193		•	Incl.		•		•	•
F571	Sundance™ 52"	160				•	•			
F572	Sundance™ 42"	161				•	•			
F574	Concept™ II Wet	146-147	•					Incl.		
F577	Concept™ I Wet	124-125	•					Incl.		
F579	Magellan®	140-141		•					Incl.	
F580	Shangri-La®	129			•		•		•	
F581	Gauguin™	154-155	•					Incl.		
F582	Rainman™	130-131		•			•		Incl.	
F588	Ultra-Max™	190-191	Incl.		•			Incl.		•
F589	Sundowner®	156-159				•	•			
F593	Traditional Concept™ 44"	88-89	•					Incl.		

• = Compatibility

Please Note: 256 Bit remote systems are not compatible with 32 Bit remote systems.

- 256 Bit systems have a Green LED and Green receiver boxes.

- 32 Bit systems have a Red LED and Black receiver boxes.

Fan Model	Fan Name	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F594	Traditional Concept™ 52"	86-87	•					Incl.		
F596	Cirque™	78-79	•					Incl.		
F598	Airus™	84-85	•					Incl.		
F601	Acero™	98-99	•					Incl.		
F602	Gyro™	118	•					Incl.		
F603	Como™	80-81	•					Incl.		
F614	Timeless	176-179		•	•	•	•		•	•
F617	Raptor	22-23						Special Remote Included RC600		
F620	Bolo™	174-175		Incl.	•		•		•	•
F647	Contractor Uni-Pack	208-209		•	•		•		•	•
F648	Contractor Uni-Pack	210-211		•	•				•	•
F659	Classica	188-189		•	•	•	•		•	•
F672	Iconic	102-103	Incl.					•		
F680	Terrana	152-153	Incl.					•		
F688	Kola	182-183		•	•	•			•	•
F689	Kola-XL	180-181	Incl.					•		
F695	Kafé	186-187		•	•	•			•	•
F696	Kafé-XL	184-185	Incl.					•		
F701	Delano®	94-95		•			•		Incl.	
F702	Volterra™	112-113		•			•		Incl.	
F705	Napoli™	110	•					Incl.		
F707	Salon Grand™	108	•					Incl.		
F711	Delano® II	96-97	•					Incl.		
F715	Napoli™ II	111	•					Incl.		
F726	Spectre	12-15						Special Remote Included RC400		
F733	Gilera	48-51	•					Incl.		
F734	Strata	138-139		Incl.	•					
F737	Moda	60-61						Special Remote Included RC500		
F738	Pancake	52-53	Incl.					•		
F745	Sabot	24-25						Special Remote Included RC600		
F753	Java	68-69		Incl.						
F759	Classica Gallery Edition	188		Incl.					•	
F802	Vintage Gyro™	116-117	•					Incl.		
F803	Artemis™	34-39	•					Incl.		
F812	Lineage™	107	•					Incl.		
F820	Santa Lucia™	106	•					Incl.		
F823	Wing	40-43						Special Remote Included RC400		
F824	Uchiwa	76-77	•					Incl.		
F828	Symbio	26-27						Special Remote Included RC400		
F833	Kewl	58-59			•	Incl.				•
F840	Craftsman™	128	•					Incl.		
F843	Wave	46-47		Incl.					•	
F844	Light Wave	44-45		Incl.					•	
F853	Aviation	28-31						Special Remote Included RC500		
F887	Xtreme	16-21						Special Remote Included RC400		
F888	Slipstream	32-33						Special Remote Included RC400		
F889	Slipstream XXL	132-137						Special Remote Included RC400		
F900	Cristafano™	109	•					Incl.		
F905	Artemis™ XL5	56-57						Special Remote Included RC600		
F1000	Dyno	164-165		Incl.					•	

Please Note: 256 Bit remote systems are not compatible with 32 Bit remote systems.
- 256 Bit systems have a Green LED and Green receiver boxes.
- 32 Bit systems have a Red LED and Black receiver boxes.

• = Compatibility

Hanging Systems



FINISH	ABDD	ABR	BCW	BG	BI	BK	BN	BN/MG	BNW	BS	BWH	CC	CF	CH	CPBR	CT	DBB	DKG	DRB	DRFF	FB	FLP	GL	GM	HT	IBR
--------	------	-----	-----	----	----	----	----	-------	-----	----	-----	----	----	----	------	----	-----	-----	-----	------	----	-----	----	----	----	-----

DR5 SERIES DOWNROD ARE 3/4" I.D.

DR500-COUPLER	•**	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR512	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR518	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR524	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR536	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR548	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR560	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR572	•	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

PRE-WIRED DOWNBRIDGE™ KIT (FOR USE WITH F528 AND F529 ONLY)

DK06-6"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK24-24"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK36-36"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK48-48"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK60-60"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK72-72"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

DOWNLINK™ KIT (FOR USE WITH F531 ONLY)

DL06-6"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL15-15"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL27-27"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL39-39"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL51-51"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL63-63"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL75-75"	-	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

MINKA-AIRE® 45° SLOPE CEILING ADAPTER KITS (SCA)

* A245 3/4" I.D.	•**	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
A180	-	•	•	-	•	•	•	-	•	•	•	-	•	•	•	•	•	•	•	-	•	-	•	-	•	•

Minka-Aire® offers a full selection of downrods in 59 finishes and 8 lengths to complement any Minka-Aire® ceiling fan.

* A245 3/4" I.D. is also available in PR (Primer) finish.

** For F524-ABD, only.



FINISH	IO	KA	LN	MCG	MG	MP	MW	ODK	ORB	PBL	PI	PN	PW	RD	RRB	RW	SI	SL	STW/GOW	SWH	TSP	VB	VP	VRT	WH/44	WHF
--------	----	----	----	-----	----	----	----	-----	-----	-----	----	----	----	----	-----	----	----	----	---------	-----	-----	----	----	-----	-------	-----

DR5 SERIES DOWNROD ARE 3/4" I.D.

DR500-COUPLER	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR512	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR518	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR524	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR536	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR548	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR560	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR572	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

PRE-WIRED DOWNBRIDGE™ KIT (FOR USE WITH F528 AND F529 ONLY)

DK06-6"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK24-24"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK36-36"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK48-48"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK60-60"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK72-72"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

DOWNLINK™ KIT (FOR USE WITH F531 ONLY)

DL06-6"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL15-15"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL27-27"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL39-39"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL51-51"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL63-63"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL75-75"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-

MINKA-AIRE® 45° SLOPE CEILING ADAPTER KITS (SCA)

* A245 3/4" I.D.	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
A180	-	•	•	•	•	•	•	•	•	•	•	•	•	•	-	-	•	-	•	•	•	-	•	•	•	•

All component parts and hardware supplied with your Minka-Aire® ceiling fan have been designed and engineered to assure proper and safe installation of your new ceiling fan. Substituting parts or hardware, such as, but not limited to the hanger ball and the hanger bracket, not supplied with your ceiling fan by Minka-Aire®, will void the Minka-Aire® Warranty.

Hanging Systems



Low Ceiling Adapter A180

For use on:

F513, F514, F522, F532, F546, F547, F548, F556, F562, F563, F568, F569, F588, F589, F596, F601, F603, F613, F614, F620, F621, F622, F647, F648, F659, F672, F688, F689, F695, F696, F734, F753, F759, F824



Slope Ceiling Adapter Kit (SCA) A245-BN


($\frac{3}{4}$ " I.D.)

U.S. Patent(s): 7,510,160

Minka-Aire® 45° Slope Ceiling Adapter Kit (SCA)

Minka-Aire® SCA Kit was designed to meet the needs of the home building industry as demand increases for higher, more steeply angled ceilings. Minka-Aire® A245 SCA is used with $\frac{3}{4}$ " I.D. DR5 Series Downrod.

Sloped Ceiling Application with standard hanging systems for slopes up to a maximum of 29°



Sloped Ceiling Installation

Minka-Aire® ceiling fans equipped with universal hanging systems may be hung from standard or vaulted ceilings up to 21° pitch.

The above kit as shown includes the mounting bracket, the angled ball assembly and locking pin. For fans that weigh in excess of 35lbs, simply use the hanging bracket that comes with the fan in the box (75lbs rating standard) and the kit's angled ball assembly and locking pin. (Fan model numbers F528, F529 and F531 do not apply because of their unique Downbridge™ hanging systems)

When ordering SCA specify finish to match your needs.

Finishes Available:

ABR, BCW, BG, BI, BK, BN, BNW, BS, BWH, CC, CF, CH, CPBR, CT, DBB, DKG, DRB, DRF, FB, FLP, GL, HT, IBR, IO, KA, LN, MCG, MG, MP, MW, ORB, PBL, PI, PN, PR, PW, RD, RRB, SI, SL, SLV, STW/GOW, SWH, TSP, VB, VP, VRT, WH, WHF

(PR - Primer finish ready for painting to match your ceiling)

F738 Fan Only



Internal Threaded Downrod

($\frac{3}{4}$ " I.D.)

	BN	DK	ORB	WHF
DR1512	•	•	•	•
DR1518	•	•	•	•
DR1524	•	•	•	•
DR1536	•	•	•	•
DR1548	N/A	•	•	•
DR1560	N/A	•	•	•
DR1572	N/A	•	•	•

Downrod sizes of 48", 60" and 72" are currently not available in BN finish.

Pre-Wired Downbridge™ Kit (for use on F528 and F529 only)



DK36

Downbridge™ Kit

Maximum length is 72"

(Size and Finish: See Page(s): 74)

Downlink™ Kit (for use on F531 only)



DL39

Downlink™ Kit

Maximum length is 72"

(Size and Finish: See Page(s): 72)

Note: It is not possible to join Downbridge™ or Downlink™ kits together for hanging fans in excess of maximum kit lengths.



Downrod Coupler

DR500

($\frac{3}{4}$ " I.D.)

For those occasions when you need to hang your ceiling fan on a longer than 72" downrod, simply use one of our downrod couplers (DR500) available in finishes to match all our fans and downrods. The coupler enables you to couple our $\frac{3}{4}$ " downrods together and hang fans on total downrod lengths of up to 144".

Universal Light Kits



K9500

Two Light
Belcaro Walnut™
60W Candelabra Base (Included)
11 ¼" Dia. x 6 ½"H



K9515-1

Three Light
Frosted White
40W Candelabra Base (Included)
12 ¼" Dia. x 2 ½"H
Includes Polished Nickel & White Caps



K9515-2

Three Light
Tea Stain
40W Candelabra Base (Included)
12 ¼" Dia. x 2 ½"H
Includes Dark Brushed Bronze & Oil Rubbed Bronze Caps



K9525-1

Three Light
Frosted White
40W Candelabra Base (Included)
12 ¼" Dia. x 2 ½"H
Includes Polished Nickel & White Caps



K9525-2

Three Light
Tea Stain
40W Candelabra Base (Included)
12 ¼" Dia. x 2 ½"H
Includes Dark Brushed Bronze & Oil Rubbed Bronze Caps



* K9548

Three Light
Etched Swirl
60W Candelabra Base (Included)
12" Dia. x 5"H



K9380-1

Two Light
French Scavo
13W GU24 Spiral CFL Base (Included)
11 ½" Dia. x 5 ½"H



K9380-2

Two Light
Excavation
13W GU24 Spiral CFL Base (Included)
11 ½" Dia. x 5 ½"H



Please Note: All Light Kits include Chain with Decorative Fob. (Not shown)

* Additional Cap Finishes Available

Universal Light Kits



*** K9369-L**

Three Light
Etched Swirl
60W Candelabra Base (Included)
13 1/4\"/>



K9372-1

Three Light
Caspian™
60W Candelabra Base (Included)
13 1/4\"/>



K9372-2

Three Light
Excavation
60W Candelabra Base (Included)
13 1/4\"/>



K9372-3

Three Light
Parchment
60W Candelabra Base (Included)
13 1/4\"/>



K9372-4

Three Light
Venetian Scavo
60W Candelabra Base (Included)
13 1/4\"/>



K9372-5

Three Light
Alabaster Dust™
60W Candelabra Base (Included)
13 1/4\"/>



*** K9363-L**

Three Light
Etched Marble
60W Candelabra Base (Included)
13 1/4\"/>



*** K9376-1**

Three Light
Caspian™
60W Candelabra Base (Included)
16\"/>



*** K9376-2**

Three Light
Excavation
60W Candelabra Base (Included)
16\"/>

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

*** Additional Cap Finishes Available**



- | | | | |
|-----------|---------------------|---------------|-------------------------------------|
| AC100 | Swirled Glass | AC100-KA | Kocoa |
| AC100-ABR | Antique Bronze | AC100-MCG | Mottled Copper with Gold Highlights |
| AC100-BCW | Belcaro Walnut™ | AC100-ORB | Oil Rubbed Bronze |
| AC100-BS | Brushed Steel | AC100-PBL | Provencal Blanc |
| AC100-BWH | Bone White | AC100-PI | Patina Iron |
| AC100-CT | Cattera Bronze™ | AC100-PW | Pewter |
| AC100-DBB | Dark Brushed Bronze | AC100-STW/GOW | Sterling Walnut™/Golden Walnut |
| AC100-EX | Excavation | AC100-SWH | Shell White |
| AC100-FB | French Beige | AC100-VRT | Vintage Rust™ |



K9373

One Light Opal Glass
50W Mini-Can Xenon (Included)
9 1/2" Dia. x 5 1/4" H
For 30"/32" Sweep Fans



K9374

One Light Opal Glass
50W Mini-Can Xenon (Included)
10 1/2" Dia. x 5 1/4" H
For 40"/44" Sweep Fans



K9375

One Light Opal Glass
50W Mini-Can Xenon (Included)
11 1/2" Dia. x 5 3/4" H
For 50"/56" Sweep Fans



Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

Wet Location

K9401

Two Light Opal Glass
13W GU24 Spiral CFL Bulbs (Included)
10 1/2" Dia. x 5 1/2" H



K9402

One Light Opal Glass
60W Candelabra Base (Included)
7 3/4" Dia. x 8 1/2" H



Finish Codes

BCW	Belcaro Walnut™	ORB	Oil Rubbed Bronze
BS	Brushed Steel	SWH	Shell White
BWH	Bone White	VRT	Vintage Rust™
HT	Heritage™	WH/44	White
MW	Mossoro Walnut™		

Universal Light Kits

K37

Four Light
40W Candelabra Base (Included)
2 1/4" Side Shade
13"Dia. x 6 1/2"H



K37-L-BCW

K1

Four Light
40W Candelabra Base (Included)
2 1/4" Side Fitter
11 3/4"Dia. x 3"H



K1-ABR



K1-L-BCW



K1-L-BS



K1-L-ORB



K1-L-SWH



K1-L-44

K1099

One Light
Opal Glass
60W Candelabra Base (Included)
8 1/2"Dia. x 6 3/4"H



K1099-1-L-44



K9365-L-44 (Low Profile)

Three Light
Etched Marble
60W Candelabra Base (Included)
12 1/2"Dia. x 4 1/2"H



GC900 SET

Optional Crystal Set
Available Only for the F900 Fan



Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

Finish Codes


ABR	Antique Bronze	BS	Brushed Steel	SWH	Shell White
BCW	Belcaro Walnut™	ORB	Oil Rubbed Bronze	WVH/44	White



K33
 Three Light
 60W Candelabra Base (Included)
 2 1/4" Side Shade
 6 1/4"Dia. x 3 1/2"H



K35
 Three Light
 13W Spiral Medium Base
 (Included)
 2 1/4" Side Shade
 7 1/4"Dia. x 3 1/2"H



Finish Codes

ABR	Antique Bronze	KA	Kocoa	VP	Vineyard Patina
BCW	Belcaro Walnut™	MCG	Mottled Copper w/Gold	WH/44	White
BN	Brushed Nickel	ORB	Oil Rubbed Bronze		
BS	Brushed Steel	PBL	Provencal Blanc		
CC	Cognac	PI	Patina Iron		
DBB	Dark Brushed Bronze	PW	Pewter		
FB	French Beige	SWH	Shell White		

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)


Universal Light Kits

K34


Four Light
13W Spiral Medium Base
(Included)
2 1/4" Side Shade
11 3/4" Dia. x 2 3/4" H




K34-BCW




K34-BN




K34-BS



K34-CC



K34-DBB



K34-KA



K34-MCG




K34-ORB




K34-PI



K34-PW



K34-SWH



K34-44

Finish Codes

BCW	Belcaro Walnut™	FB	French Beige	PI	Patina Iron
BN	Brushed Nickel	KA	Kocoa	PW	Pewter
BS	Brushed Steel	MCG	Mottled Copper w/Gold	SWH	Shell White
CC	Cognac	ORB	Oil Rubbed Bronze	VP	Vineyard Patina
DBB	Dark Brushed Bronze	PBL	Provencal Blanc	WH/44	White

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)



Custom Light Kits



K9614-DBB



K9614-FB



K9614-MCG

K9614

Three Light
60W Candelabra Base (Included)
2 1/4" Side Shade
8 1/2"Dia. x 3 1/4"H

Compatible with the
F614 Timeless Fans Only



K9614-ORB



K9614-PI



K9614-PW



K9659-BCW



K9659-DRF



K9659-FB

K9659

Three Light
60W Candelabra Base (Included)
2 1/4" Side Shade
7 1/2"Dia. x 3 1/2"H

Compatible with the
F659 Classica Fans Only



K9659-MCG



K9659-PBL



K9659-PI

Finish Codes


BCW	Belcaro Walnut™	FB	French Beige	PBL	Provencal Blanc
DBB	Dark Brushed Bronze	MCG	Mottled Copper w/Gold	PI	Patina Iron
DRF	Driftwood	ORB	Oil Rubbed Bronze	PW	Pewter

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

Accessory Fan Blades




CW
Cherry Wood



DC
Dark Cherry



DM
Dark Maple



DW
Dark Walnut



LC
Light Cherry



LM
Light Maple



ML
Reversible
Medium Oak



MM
Medium Maple

Fan Blade Compatibility Chart

Model	Fan Name	CW	DC	DM	DW	LC	LM	ML	MM	MO
F516	Concept™ I	N/A	N/A	FB216-DM	FB216-DW	N/A	N/A	N/A	N/A	N/A
F517	Concept™ I	N/A	N/A	FB217-DM	FB217-DW	N/A	N/A	N/A	N/A	N/A
F518	Concept™ II	N/A	N/A	FB216-DM	FB216-DW	N/A	N/A	N/A	N/A	N/A
F519	Concept™ II	N/A	N/A	FB217-DM	FB217-DW	N/A	N/A	N/A	N/A	N/A
F528	San Francisco®	FB106-CW	N/A	N/A	N/A	N/A	N/A	N/A	FB106-MM	N/A
F529	San Francisco®	FB106-CW	N/A	N/A	N/A	N/A	N/A	N/A	FB106-MM	N/A
F547	Contractor	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A
F548	Contractor Uni-Pack	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A
F562	Supra® 32"	N/A	FB422-DC	FB422-DM	FB422-DW	FB422-LC	FB422-LM	N/A	FB422-MM	N/A
F563	Supra® 44"	N/A	FB423-DC	FB423-DM	FB423-DW	FB423-LC	FB423-LM	N/A	FB423-MM	N/A
F568	Supra® 52"	N/A	FB424-DC	FB424-DM	FB424-DW	FB424-LC	FB424-LM	N/A	FB424-MM	N/A
F588	Ultra-Max™ 54"	FB107T-CW	N/A	N/A	FB107T-DW	FB107T-LC	N/A	N/A	FB107T-MM	N/A
F589	Sundowner®	N/A	N/A	FB107P-DM	FB107P-DW	N/A	N/A	N/A	FB107P-MM	N/A
F596	Cirque™	Optional Blades Sets are the FB196-RYB (Multi-colored, Red, Yellow, Blue) and the FB196-MG (Mahogany Finish)								



Fan Blade Compatibility Chart

Model	Fan Name	NM	NP	NW	ORB	RW	SL	SWH	WO	WP
F516	Concept™ I	N/A	N/A	N/A	FB216-ORB	N/A	N/A	N/A	N/A	N/A
F517	Concept™ I	N/A	N/A	N/A	FB217-ORB	N/A	N/A	N/A	N/A	N/A
F518	Concept™ II	N/A	N/A	N/A	FB216-ORB	N/A	N/A	N/A	N/A	N/A
F519	Concept™ II	N/A	N/A	N/A	FB217-ORB	N/A	N/A	N/A	N/A	N/A
F528	San Francisco®	N/A	N/A	N/A	N/A	N/A	FB106-SL	N/A	N/A	N/A
F529	San Francisco®	N/A	N/A	N/A	N/A	N/A	FB106-SL	N/A	N/A	N/A
F547	Contractor	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP
F548	Contractor Uni-Pack	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP
F562	Supra® 32"	N/A	N/A	FB422-NW	N/A	N/A	FB422-SL	N/A	FB422-WO	FB422-WP
F563	Supra® 44"	N/A	N/A	FB423-NW	N/A	N/A	FB423-SL	N/A	FB423-WO	FB423-WP
F568	Supra® 52"	N/A	N/A	FB424-NW	N/A	N/A	FB424-SL	FB424-SWH	FB424-WO	FB424-WP
F588	Ultra-Max™ 54"	N/A	FB107T-NP	FB107T-NW	N/A	FB107T-RW	N/A	N/A	FB107T-WO	FB107T-WP
F589	Sundowner®	N/A	N/A	N/A	N/A	N/A	N/A	FB107P-SWH	N/A	N/A
F596	Cirque™	Optional Blades Sets are the FB196-RYB (Multi-colored, Red, Yellow, Blue) and the FB196-MG (Mahogany Finish)								

2 1/4" Glass Shades



2010

Frosted/Ribbed
4 1/4" Dia. x 5"H



2018A

Opal
4 3/4" Dia. x 4 1/2"H



*** 2548**

Etched Opal
5 3/4" Dia. x 4 1/2"H



*** 2549**

Etched Marble
5 3/4" Dia. x 4 1/2"H



*** 2560**

Frosted/Clear
5" Dia. x 4 3/4"H



2565

Etched Seeded
4 3/4" Dia. x 4 3/4"H



2567

Etched Marble
5 1/4" Dia. x 4 3/4"H



*** 2593-1**

Aged Champagne
5" Dia. x 5 1/4"H

* An Original Minka Group® Design



* 2593-2

Excavation
5"Dia. x 5 1/4"H



* 2593-4

Venetian Scavo
5"Dia. x 5 1/4"H



* 2593-5

French Cream
5"Dia. x 5 1/4"H



2632

Salon Scavo™
5"Dia. x 4 3/4"H



2636

Tuscan Scavo
5"Dia. x 4 3/4"H



2645

Linen
5"Dia. x 5 1/4"H



2646

Tuscan Scavo
5"Dia. x 5 1/4"H



2648

Etched Marble with Toned Edges
5 1/2"Dia. x 5"H



4099

4" Opal Glass Shade
8 1/2"Dia. x 5 1/2"H

Bulb Reference



Watts: 10W / 20W
XENON JCX 12V
G4 BI-PIN BASE

Frosted JX4-20 (20W)
Clear JX4C-10 (10W)
JX4C-20 (20W)



Watts: 35W / 50W
XENON JCX 12V
GY6.35 BI-PIN BASE

Frosted JX6-35 (35W)
JX6-50 (50W)



Watts: 25W / 35W / 40W / 60W / 75W
G9 XENON 120V
G9 BASE

Frosted JX9-025 (25W)
JX9-035 (35W)
JX9-040 (45W)
JX9-060 (60W)
JX9-075 (75W)
Clear JX9C-025 (25W)
JX9C-040 (40W)



Watts: 20W / 50W
XENON 120V
DC (BAYONET)

JXB15-20 (20W)
JXB15-50 (50W)



Watts: 75W
XENON 120V
E12 (CANDELABRA) BASE

Frosted JDXF-12-075 (75W)



Watts: 50W / 75W / 100W
MINI-CAN XENON 120V
E11 (CANDELABRA) BASE

Frosted JDX-050 (50W)
JDX-75 (75W)



Watts: 50W / 75W / 100W
MINI-CAN HALOGEN 120V
E11 (CANDELABRA) BASE

Frosted JD-50 (50W)
JD-75 (75W)
JD-100 (100W)
Clear JDC-50 (50W)
JDC-75 (75W)
JDC-100 (100W)




Watts: 50W
JDD XENON 120V
E12 (CANDELABRA) BASE

JDX2-050 (50W) Clear
JDX2F-050 (50W) Frosted



Watts: 100W / 150W
78MM 120V DOUBLE ENDED
HALOGEN (J-TYPE)
R7S BASE

JB-100 (100W)
JB-150 (150W)



Watts: 8W DC / 10W AC
LED MODULE

L-L8-MD590
L-AC10-MODULE



Watts: 50W
PAR16 HALOGEN
E26 (MEDIUM) BASE

PAR16-50 (50W)



Watts: 35W / 50W
XENON JCX 12V
GU10 BASE

JGU-035 (35W)
JGU-50 (50W)



Watts: 20W / 35W / 50W
HALOGEN MR16
GX5.3 BI-PIN BASE

Clear JMR16-C-20 (20W 12V)
JMR16-C-35 (35W 12V)
JMR16-C-50 (50W 12V)
Frosted JMR16-20 (20W 120V)
JMR16-35 (35W 120V)
JMR16-50/120V (50W 120V)



Watts: 13W / 26W
SPIRAL CFL
E26 (MEDIUM) BASE

FLB-13S (13W)




Watts: 13W / 26W
SPIRAL CFL
GU24 BASE

FLB-13M (13W)
FLB-26M (26W)



Watts: 18W / 26W
SQUAT SPIRAL CFL
GU24 BASE

FLS-18M (18W)
FLS-26M (26W)



Watts: 40W
FERRO
E26 (MEDIUM) BASE

E26-FW1910-40W (40W)



Watts: 40W / 60W / 100W
T10 120V
E26 (MEDIUM) BASE

Clear JT10-040C (40W)
JT10-060C (60W)
JT10-100C (100W)
Frosted JT10-060F (60W)



Watts: 27W
FULL 24 CFL
GX10q-4 BASE

JT4-27 (27W)



Watts: 13W
4-PIN (PL-C)
G24q-1 BASE

FLT-13Q (13W)



Watts: 27W
CFL
GX10q-4 BASE

JT2-27 (27W)



Watts: 32W
FC12T9 T9 CIRCULINE
G10Q

FLC-22 (22W)
FLC-32 (32W)
FLC-40 (40W)



Watts: 8W / 13W
FLUORESCENT
T5 G13 BI-PIN BASE

Ballast: BLST08-T5
JT5-8
JT5-13



Watts: 7W
C7 CFL
E12 (CANDELABRA) BASE

FLB-07C (7W)



Watts: 75W
MR16
E17 BASE

JDR-75 (75W)



Watts: 40W / 60W
B10.5
E12 (CANDELABRA) BASE



Watts: 60W
BR30
E26 (MEDIUM) BASE



Watts: 40W / 60W
A15
E26 (MEDIUM) BASE



Watts: 40W / 60W / 75W / 100W
A19
E26 (MEDIUM) BASE



Watts: 150W
A21 (3-WAY)
E26 (MEDIUM) BASE



Watts: 25W / 40W / 60W
G16 1/2
E12 (CANDELABRA) BASE



Watts: 60W / 100W
G25
E26 (MEDIUM) BASE



Watts: 60W / 100W
G30
E26 (MEDIUM) BASE



Watts: 40W / 60W / 100W
G40
E26 (MEDIUM) BASE

ACCESSORIES

AC100	230
AC100-ABR	230
AC100-BCW	230
AC100-BS	230
AC100-BWH	230
AC100-CT	230
AC100-DBB	230
AC100-EX	230
AC100-FB	230
AC100-KA	230
AC100-MCG	230
AC100-ORB	230
AC100-PBL	230
AC100-PI	230
AC100-PW	230
AC100-STW/GOW	230
AC100-SWH	230
AC100-VRT	230
GC900 SET	109, 232

ACCESSORY BLADES

FB103S-DM	236
FB103S-DW	236
FB103S-LC	236
FB103S-LM	236
FB103S-ML	236
FB103S-MM	236
FB103S-NM	237
FB103S-NW	237
FB103S-RW	237
FB103S-SL	237
FB103S-SWH	237
FB103S-WO	237
FB103S-WP	237
FB106-CW	236
FB106-MM	236
FB106-SL	237
FB107P-DM	236
FB107P-DW	236
FB107P-MM	236
FB107P-SWH	237
FB107T-CW	236
FB107T-DW	236
FB107T-LC	236
FB107T-MM	236
FB107T-NP	237
FB107T-NW	237
FB107T-RW	237
FB107T-WO	237
FB107T-WP	237

FB196-MG	78, 236, 237
FB196-RYB	79, 236, 237
FB216-DM	236
FB216-DW	236
FB216-ORB	237
FB217-DM	236
FB217-DW	236
FB217-ORB	237
FB422-DC	236
FB422-DM	236
FB422-DW	236
FB422-LC	236
FB422-LM	236
FB422-MM	236
FB422-NW	237
FB422-SL	237
FB422-WO	237
FB422-WP	237
FB423-DC	236
FB423-DM	236
FB423-DW	236
FB423-LC	236
FB423-LM	236
FB423-MM	236
FB423-NW	237
FB423-SL	237
FB423-WO	237
FB423-WP	237
FB424-DC	236
FB424-DM	236
FB424-DW	236
FB424-LC	236
FB424-LM	236
FB424-MM	236
FB424-NW	237
FB424-SL	237
FB424-SWH	237
FB424-WO	237
FB424-WP	237

CEILING FANS

F300-BN	100
F300-ORB	100
F302-BN	120
F302-RRB	120
F315-KA	101
F315-SL	101
F402-BNW	119, 162
F402-ORB	119, 162
F470-BN	172
F470-ORB	173

F470-WH	173
F474-ORB	146
F474-WH	146
F476-ORB	125
F476-WH	125
F477-BNW	123
F477-ORB	122
F477-WH	122
F502-BCW	115
F502-PBL	115
F510-BS	90
F510-ORB	91
F510-WH	90
F513-BN	92
F513-KA	93
F513-ORB	92
F513-WH	93
F514-BN	82
F514-ORB	82
F514-WH	83
F516-BN	67
F516-ORB	66
F516-PN	67
F516-WH	66
F517-BN	67
F517-ORB	66
F517-PN	67
F517-WH	66
F518-BN	64
F518-ORB	65
F518-PN	65
F518-WH	64
F519-BN	62
F519-MG	63
F519-ORB	62
F519-PN	62
F519-WH	63
F521-ABD	70
F521-ORB	70
F521-WHF	71
F522-BN	168
F522-BWH	169
F522-ORB	169
F522-ORB/TS	168
F522-WH	169
F523-ABD	142
F523-ORB	142
F523-WHF	143
F524-ABD	54
F524-DK	55

F524-ORB	55
F524-WHF	55
F528-L-BS/CH	74
F529-L-BS/CH	75
F529-L-ORB	74
F531-L-BN	72
F531-L-BN/MG	73
F531-L-WH	72
F532-BNW	127
F532-BWH	126
F532-DRF	127
F532-ORB	127
F533-BN	170
F533-BWH	171
F533-DK	170
F533-ORB	171
F533-WH	170
F539-BCW	104
F539-BN	105
F539-ORB	105
F544-BCW	114
F544-GBZ	114
F546-BS	218
F546-BS/DW	219
F546-ORB	218
F546-WH	219
F547-ABR	216
F547-BS	217
F547-BS/DW	217
F547-BWH	217
F547-ORB	216
F547-WH	217
F548-BS	214
F548-BS/DW	215
F548-BWH	214
F548-ORB	212
F548-ORB/EX	213
F548-WH	212
F556-BN	206
F556-BN/DW	207
F556-BWH	206
F556L-BN	204
F556L-BN/DW	205
F556L-BWH	204
F556L-ORB	205
F556-ORB	207
F562-BS	203
F562-ORB	203
F562-WH	202
F563-BS	200

Index

F563-BS/DW	200
F563-ORB	201
F563-SP	198
F563-SP-BS/DW	198
F563-SP-ORB	199
F563-SP-WH	199
F563-WH	201
F565-WH	220
F566-WH	220
F568-BCW	196
F568-BS	197
F568-BS/DW	195
F568-BWH	194
F568-KA	194
F568-ORB	197
F568-SWH	195
F568-WH	196
F569-BS	192
F569-BS/DW	193
F569-ORB	192
F569-WH	193
F571-DRF	160
F571-ORB	160
F571-WH	160
F572-ORB	161
F572-WH	161
F574-BNW	147
F577-BNW	124
F579-L-BNW	140
F579-L-ORB	141
F580-VR/BB	129
F581-BG	154
F581-ORB	155
F581-WHF	155
F582-BNW	130
F582-GL	131
F582-ORB	130
F588-SP-BCW	191
F588-SP-BN	190
F588-SP-BWH	191
F588-SP-WH	190
F589-BI/AI	159
F589-BWH	156
F589-DRF	157
F589-HT	158
F589-MW	157
F589-ORB	156
F589-SWH	157
F589-VRT	159
F589-WH	158

F593-ORB	89, 151
F593-PW	88, 150
F593-WH	89, 151
F594-ORB	86, 148
F594-PW	87, 149
F594-WH	87, 149
F596-BN	78, 79
F596-PN/TL	79
F598-BN	85
F598-ORB	84
F598-WH	85
F601-BS/BN	98
F601-BS/MG	98
F601-ORB	99
F601-PN	99
F602-BN/CH	118
F602-RRB	118
F603-BN	81
F603-ORB	80
F603-WH	80
F614-DBB	176
F614-FB	178
F614-MCG	177
F614-ORB	179
F614-PI	177
F614-PW	178
F617-BN	23
F617-GM	22
F617-ORB/AB	23
F617-WH	22
F620-BCW	175
F620-BN	174
F620-DBB	175
F620-ORB	174
F622-BWH	166
F622-ORB	166
F622-ORB/TS	167
F622-PW	167
F647-BS	208
F647-ORB	209
F647-ORB/TS	209
F647-SWH	208
F647-WH	209
F648-BS	210
F648-ORB	211
F648-ORB/EX	211
F648-WH	211
F659-BCW	189
F659-DRF	189
F659-FB	189

F659-PBL	188
F659-PI	189
F672-MBK/BN	103
F672-ORB	102
F672-ORB/AB	103
F672-WH/BN	102
F680-BG	153
F680-KA	152
F688-DBB	183
F688-KA	182
F688-PW	182
F688-WH	183
F689-DBB	181
F689-KA	180
F689-PW	180
F689-WH	181
F695-CC	187
F695-KA	186
F695-VP	187
F695-WH	187
F696-CC	184
F696-KA	184
F696-VP	185
F696-WH	185
F701-DRB	94
F701-DRF	95
F701-KA	95
F701-PN	95
F701-PW	94
F702-BCW	113
F702-VB	112
F705-STW	110
F705-TSP	110
F707-FLP	108
F711-DRB	96
F711-PN	97
F711-PW	97
F715-STW	111
F715-TSP	111
F726-BN/ORG	13
F726-BN/SL	12
F726-ORB/AB	14
F726-ORB/BN	15
F726-WHF/BN	13, 14
F733-BK/RW	48
F733-BS/BN	50
F733-PN	50
F733-SL	49
F733-WH	51
F734-GL	139

F734-ORB	138
F734-SI	139
F737-BN	60
F737-ORB	60
F737-WH	61
F738-BN	52
F738-DK	53
F738-ORB	52
F738-WHF	53
F745-BN	25
F745-DK	24
F745-ORB	25
F753-BNW	68, 145
F753-KA	68, 144
F753-PN	69
F753-WHF	69, 145
F759-PBL	188
F802-BN/CH	117
F802-KA	116
F802-ORB	117
F803-BK	39
F803-CPBR	37
F803-DK	34
F803-LN	34
F803-MG	35
F803-MP	39
F803-RD	36
F803-SL	37
F803-TL	38
F803-WH	38
F812-IO	107
F820-CT	106
F820-IBR	106
F823-DK	40
F823-MG	42
F823-MP	43
F823-SL	43
F823-WH	41
F824-BK/CH	77
F824-ORB/TB	76
F824-WH	77
F828-BN	26
F828-BN/DW	27
F828-BN/WH	27
F828-ORB	26
F828-WHF	26
F833-BK	59
F833-RD	58
F833-SL	59
F833-WH	58

F840-CF	128
F843-DK	47
F843-SL	46
F843-WH	47
F844-DK	44
F844-SL	45
F844-WH	45
F853-BN/DK	28
F853-BN/MM	31
F853-BN/SL	31
F853-RW	29
F853-WH	30
F887-72-BN	17
F887-72-ORB	20
F887-80-BN	17
F887-80-ORB	20
F887-88-BN	17
F887-88-ORB	20
F887-96-BN	17
F887-96-ORB	20
F888-BNW	32
F888-DK	33
F888-ORB	33
F888-WHF	33
F889-BNW	133
F889-ORB	137
F889-SI	135
F900-BCW	109
F905-DK	57
F905-SL	56
F905-WH	57
F1000-BN	163, 164
F1000-ORB	165
F1000-WH	165

CEILING MEDALLIONS

CM1550-FLP	108
CM7022-STW	110
CM7022-TSP	110
CM7038-STW	111
CM7038-TSP	111
CM8222-IBR	106

CONTROL SYSTEMS

RC400	222
RC500	222
RC600	222
RCS212	222
RCS213	222
RCS223	222
WC105-WH	223

WC106-WH	223
WC110	223
WCS212	223
WCS213	223
WCS223	223

GLASS SHADES

2010	238
2018A	238
2548	238
2549	238
2560	238
2565	238
2567	238
2593-1	238
2593-2	239
2593-4	239
2593-5	239
2632	239
2636	239
2645	239
2646	239
2648	239
4099	239

HANGING SYSTEMS

A180	226, 227, 228
A245	226, 227
A245-BN	228
DK06	226, 227
DK24	226, 227
DK36	226, 227, 228
DK48	226, 227
DK60	226, 227
DK72	226, 227
DL06	226, 227
DL15	226, 227
DL27	226, 227
DL39	226, 227, 228
DL51	226, 227
DL63	226, 227
DL75	226, 227
DR235	73
DR500	226, 227, 228
DR512	226, 227
DR518	226, 227
DR524	226, 227
DR536	226, 227
DR548	226, 227
DR560	226, 227
DR572	226, 227

DR1512	228
DR1518	228
DR1524	228
DR1536	228
DR1548	228
DR1560	228
DR1572	228

LIGHT KITS - CUSTOM

K9614-DBB	235
K9614-FB	235
K9614-MCG	235
K9614-ORB	235
K9614-PI	235
K9614-PW	235
K9659-BCW	235
K9659-DRF	235
K9659-FB	235
K9659-MCG	235
K9659-PBL	235
K9659-PI	235

LIGHT KITS - UNIVERSAL

K1-ABR	232
K1-L-44	232
K1-L-BCW	232
K1-L-BS	232
K1-L-ORB	232
K1-L-SWH	232
K33-L-44	233
K33-L-BS	233
K33-L-DBB	233
K33-L-FB	233
K33-L-MCG	233
K33-L-ORB	233
K33-L-PI	233
K34-44	234
K34-BCW	234
K34-BN	234
K34-BS	234
K34-CC	234
K34-DBB	234
K34-KA	234
K34-MCG	234
K34-ORB	234
K34-PI	234
K34-PW	234
K34-SWH	234
K35-44	233
K35-BCW	233
K35-BN	233





K35-BS	233
K35-CC	233
K35-DBB	233
K35-FB	233
K35-KA	233
K35-MCG	233
K35-ORB	233
K35-PBL	233
K35-PI	233
K35-PW	233
K35-SWH	233
K35-VP	233
K37-L-BCW	232
K1099-1-L-44	232
K9363-L	230
K9365-L-44	232
K9369-L	230
K9372-1	230
K9372-2	230
K9372-3	230
K9372-4	230
K9372-5	230
K9373-L-BS	231
K9373-L-ORB	231
K9373-L-WH	231
K9374-L-BS	231
K9374-L-WH	231
K9375-L-BS	231
K9375-L-BWH	231
K9375-L-ORB	231
K9375-L-WH	231
K9376-1	230
K9376-2	230
K9380-1	229
K9380-2	229
K9401-L-BWH	231
K9401-L-DRF	231
K9401-L-HT	231
K9401-L-MW	231
K9401-L-ORB	231
K9401-L-VRT	231
K9401-L-WH	231
K9402-L-44	231
K9402-L-ORB	231
K9500	229
K9515-1	229
K9515-2	229
K9525-1	229
K9525-2	229
K9548	229

Room Size and Ceiling Height Recommendations




ROOM SIZE

These measurements are for general air flow requirements only. Decorating plans or aesthetic considerations should influence your fan choices beyond these room size specifications. For very large rooms, multiple fans is an option.

				
Blade Sweep	26"-42"	44"	52"-54"	60"-72"
Approximate Room Size	6' x 8' 40-60 sq. ft.	8' x 10' 70-90 sq. ft.	10' x 12' 100-150 sq. ft.	12' x 15' (Great Room) Over 160 sq. ft.

CEILING HEIGHT

Be sure there is at least 7 feet of clearance under your ceiling fan blades. The standard 3½" and 6" downrods should work in most 8 feet ceiling installations. This will position the blades far enough from the ceiling to have enough "supply" air above the blades to provide good air movement. If greater floor to fan clearance is needed, some fans can use our low ceiling adapter (A180) without using any downrod. However, air movement is reduced using the low ceiling adapter. This chart shows recommended downrod lengths for various ceiling heights.



Notes

Notes

		Page Number	Blade Sweep	No. of Blades	Blade Pitch	Motor Size (m/m)	RPM (Hi/Low)	Warranty	Light Kit	Downrods ¾" I.D.	Downrods ½" I.D.	Lead Wire	Dimensions A	Dimensions B	Hanging Weight
F300	Retro Style Fan	100	10"	3	14°	70 x 70	1253/1525	One Year	N/A	N/A	N/A	72"	N/A	N/A	6 lbs
F302	Gyrette™	120	10"	8	14°	82 x 25	1555/1328	Lifetime	N/A	4½"	N/A	54"	14"	18"	18 lbs
F315	Hassock Aire	101	12"	3	14°	N/A	N/A	One Year	N/A	N/A	N/A	112"	N/A	N/A	15 lbs
F402	Gyro™ Wet	119,162	42"	6	20°	82 x 25	1360/720	Lifetime	Integrated	3½" & 6"	N/A	80"	18½"	17"	28 lbs
F470	Hilo	172-173	52"	5	12°	153 x 17	173/69	Lifetime	N/A	3½" & 6"	N/A	80"	16"	9½"	18 lbs
F474	Concept™ II Wet 52"	146-147	52"	3	14°	188 x 20	168/90	Lifetime	Integrated	N/A	N/A	8"	11¾"	9"	26 lbs
F476	Concept™ I Wet 52"	124-125	52"	3	14°	188 x 20	166/91	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	13¾"	26 lbs
F477	Concept™ I Wet 58"	122-123	58"	3	14°	188 x 22	171/102	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	12"	30 lbs
F502	Traditional Gyro™	115	42"	6	20°	80 x 25	1360/720	Lifetime	Integrated	3½" & 12"	N/A	80"	19¾"	16½"	35 lbs
F510	Spacesaver	90-91	26"	3	14°	153 x 12	392/120	Lifetime	Integrated	N/A	N/A	8"	11"	6¼"	11 lbs
F513	New Era	92-93	52"	4	14°	172 x 16	199/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	11¾"	18 lbs
F514	Zen	82-83	52"	4	14°	172 x 16	187/63	Lifetime	Integrated	3½" & 6"	N/A	80"	16¼"	11¾"	23 lbs
F516	Concept™ I 44"	66-67	44"	3	14°	153 x 15	190/80	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	13"	21 lbs
F517	Concept™ I 52"	66-67	52"	3	14°	172 x 20	180/70	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	13"	25 lbs
F518	Concept™ II 44"	64-65	44"	3	14°	153 x 15	184/86	Lifetime	Integrated	N/A	N/A	8"	11½"	9½"	23 lbs
F519	Concept™ II 52"	62-63	52"	3	14°	172 x 20	179/70	Lifetime	Integrated	N/A	N/A	8"	11½"	9½"	26 lbs
F521	Aluma	70-71	52"	4	12°	153 x 15	160/63	Lifetime	Integrated	3½" & 6"	N/A	80"	13½"	11¾"	20 lbs
F522	Mojo	168-169	52"	5	12°	153 x 15	162/60	Lifetime	Included	3½" & 6"	N/A	80"	17½"	12¼"	27 lbs
F523	Aluma Wet	142-143	52"	4	12°	153 x 20	160/63	Lifetime	Integrated	3½" & 6"	N/A	80"	13"	11"	23 lbs
F524	Roto	54-55	52"	3	22°	153 x 15	212/74	Lifetime	N/A	3½" & 6"	N/A	80"	10½"	9"	20 lbs
F528	San Francisco®	74	56"	3	13°	172 x 17	200/72	Lifetime	N/A	N/A	12" DB	6"	20¾"	18¾"	19 lbs
F529	San Francisco®	74-75	56"	3	13°	172 x 17	200/72	Lifetime	Integrated	N/A	12" DB	6"	23½"	18½"	22 lbs
F531	Flyte®	72-73	56"	3	14°	188 x 25	180/80	Lifetime	Integrated	N/A	9" DL	80"	18"	17½"	26 lbs
F532	Sunseeker	126-127	60"	5	14°	188 x 25	133/48	Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	13½"	30 lbs
F533	Mojo II	170-171	52"	4	14°	153 x 15	166/82	Lifetime	Integrated	N/A	N/A	12"	13"	7½"	22 lbs
F539	Great Room Traditional	104-105	72"	5	14°	212 x 25	120/60	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	12¼"	30 lbs
F544	Calais™	114	52"	5	14°	172 x 17	170/65	Lifetime	Integrated	N/A	N/A	8"	12"	8"	28 lbs
F546	Contractor 42"	218-219	42"	5	12°	153 x 10	240/106	Lifetime	Adaptable	4"	N/A	80"	11½"	9¼"	11 lbs
F547	Contractor 52"	216-217	52"	4/5	12°	153 x 13	162/67	Lifetime	Adaptable	4"	N/A	80"	12¾"	10¼"	13 lbs
F548	Contractor Uni-Pack	208-215	52"	5	12°	153 x 13	160/56	Lifetime	Included	4"	N/A	80"	17½"	9¾"	17 lbs
F556	Contractor Plus	206-207	52"	5	12°	153 x 15	160/155	Lifetime	Adaptable	3½" & 6"	N/A	80"	12¼"	10½"	17 lbs
F556L	Contractor LED	204-205	52"	5	12°	153 x 15	160/155	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	10¾"	17 lbs
F562	Supra® 32"	202-203	32"	6	22°	153 x 16	262/95	Lifetime	Adaptable	3½" & 6"	N/A	80"	12½"	12"	14 lbs
F563	Supra® 44"	200-201	44"	5	14°	188 x 15	259/79	Lifetime	Adaptable	3½" & 6"	N/A	80"	12½"	12"	18 lbs
F563	Supra® 44" -SP	198-199	44"	5	14°	188 x 15	259/79	Lifetime	Included	3½" & 6"	N/A	80"	16½"	12"	20 lbs
F565	Mesa™ 52"	220	52"	5	12°	153 x 14	175/64	Lifetime	Adaptable	N/A	N/A	8"	8¾"	7¾"	14 lbs
F566	Mesa™ 42"	220	42"	5	12°	153 x 10	215/108	Lifetime	Adaptable	N/A	N/A	8"	8"	6¾"	11 lbs
F568	Supra® 52"	194-197	52"	5	14°	188 x 15	181/54	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	11¼"	21 lbs
F569	Supra® 52"	192-193	52"	5	14°	188 x 15	170/50	Lifetime	Included	3½" & 6"	N/A	80"	16¾"	12¼"	25 lbs
F571	Sundance™ 52"	160	52"	5	12°	153 x 15	170/70	Lifetime	Adaptable	3½" & 6"	N/A	80"	12"	12¾"	16 lbs
F572	Sundance™ 42"	161	42"	5	12°	153 x 10	210/95	Lifetime	Adaptable	3½" & 6"	N/A	80"	12¼"	10½"	12 lbs
F574	Concept™ II Wet 52"	146-147	52"	3	14°	188 x 20	158/80	Lifetime	Integrated	N/A	N/A	8"	11¾"	9"	26 lbs
F577	Concept™ I Wet 52"	124-125	52"	3	14°	188 x 20	158/80	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	13¾"	26 lbs
F579	Magellan®	140-141	60"	5	16°	188 x 25	135/62	Lifetime	Included	3½" & 6"	N/A	80"	16½"	8½"	27 lbs
F580	Shangri-La®	129	52"	5	14°	188 x 20	169/57	Lifetime	Included	3½" & 6"	N/A	80"	21¾"	13¼"	33 lbs
F581	Gauguin™	154-155	52"	4	14°	188 x 20	140/70	Lifetime	Integrated	3½" & 6"	N/A	80"	14"	14¾"	27 lbs
F582	Rainman™	130-131	54"	5	14°	172 x 20	145/70	Lifetime	Integrated	3½" & 6"	N/A	80"	24"	13½"	27 lbs
F588	Ultra-Max™ -SP	190-191	54"	5	14°	188 x 25	182/76	Lifetime	Adaptable	3½" & 6"	N/A	80"	12"	9½"	20 lbs
F589	Sundowner®	156-159	54"	5	16°	188 x 20	166/53	Lifetime	Adaptable	3½" & 6"	N/A	80"	12"	11¼"	28 lbs
F593	Traditional Concept™ 44"	88-89	44"	3	14°	153 x 17	195/83	Lifetime	Integrated	N/A	N/A	8"	11"	7½"	23 lbs
F594	Traditional Concept™ 52"	86-87	52"	3	14°	172 x 20	180/70	Lifetime	Integrated	N/A	N/A	8"	11"	7½"	26 lbs

SPECIFICATIONS

Minka-Aire® ceiling fans are warranted to be free from defects in material and workmanship only if purchased from an authorized Minka-Aire® distributor:

Fan motor - Limited Lifetime Warranty to original purchaser with proof of purchase as long as fan remains in its original installation location and is installed using only the original hardware provided (including hanger bracket).

All other parts & controls - warranted to original purchaser with proof of purchase for one (1) year from date of purchase.

		Page Number	Blade Sweep	No. of Blades	Blade Pitch	Motor Size (m/m)	RPM (Hi/Low)	Warranty	Light Kit	Downrods ¾" I.D.	Downrods ½" I.D.	Lead Wire	Dimensions A	Dimensions B	Hanging Weight
F596	Cirque™	78-79	54"	6	14°	188 x 25	125/65	Lifetime	Integrated	4" & 6"	N/A	80"	15"	10½"	26 lbs
F598	Airus™	84-85	54"	5	14°	188 x 18	183/65	Lifetime	Integrated	3½" & 6"	N/A	80"	14"	10"	26 lbs
F601	Acero™	98-99	52"	3	14°	188 x 15	183/74	Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	11½"	24 lbs
F602	Gyro™	118	42"	6	20°	82 x 25	1360/720	Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	16"	28 lbs
F603	Como™	80-81	54"	5	14°	188 x 20	170/70	Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	12¼"	28 lbs
F614	Timeless	176-179	54"	5	14°	188 x 15	161/57	Lifetime	Adaptable	3½" & 6"	N/A	80"	14"	12¾"	22 lbs
F617	Raptor	22-23	60"	5	14°	DC172 x 12	150/60	Lifetime	Integrated	3½" & 6"	N/A	80"	15¼"	8½"	29 lbs
F620	Bolo™	174-175	52"	5	14°	172 x 17	170/70	Lifetime	Included	3½" & 6"	N/A	80"	20"	11½"	29 lbs
F622	Traditional Mojo	166-167	52"	5	12°	153 x 15	162/60	Lifetime	Included	3½" & 6"	N/A	80"	15"	9½"	23 lbs
F647	Contractor Uni-Pack	208-209	52"	5	12°	153 x 13	162/67	Lifetime	Included	4"	N/A	80"	17¾"	10½"	15 lbs
F648	Contractor Uni-Pack	210-211	52"	5	12°	153 x 15	180/60	Lifetime	Included	4"	N/A	80"	18¾"	9½"	17 lbs
F659	Classica	188-189	54"	5	14°	172 x 16	187/63	Lifetime	Adaptable	3½" & 6"	N/A	80"	14"	11¾"	24 lbs
F672	Iconic™	102-103	60"	5	12°	188 x 20	160/57	Lifetime	Integrated	3½" & 6"	N/A	80"	16¾"	14½"	35 lbs
F680	Terrana	152-153	52"	2	14°	172 x 17	145/68	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	14"	33 lbs
F688	Kola	182-183	52"	5	12°	172 x 14	168/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13¼"	11"	22 lbs
F689	Kola-XL	180-181	60"	5	14°	188 x 20	145/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13¼"	11"	22 lbs
F695	Kafé	186-187	52"	5	12°	172 x 14	168/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	11"	22 lbs
F696	Kafé-XL	184-185	60"	5	14°	188 x 20	145/64	Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	11"	22 lbs
F701	Delano®	94-95	52"	5	14°	172 x 20	172/74	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	8¾"	26 lbs
F702	Volterra™	112-113	52"	5	14°	172 x 20	172/74	Lifetime	Integrated	3½" & 6"	N/A	80"	15¼"	8½"	26 lbs
F705	Napoli™	110	56"	5	14°	188 x 25	144/81	Lifetime	Integrated	3½" & 12"	N/A	80"	16¼"	10¾"	40 lbs
F707	Salon Grand™	108	56"	5	14°	188 x 25	144/81	Lifetime	Integrated	3½" & 10"	N/A	80"	16¼"	7¼"	38 lbs
F711	Delano® II	96-97	52"	5	14°	172 x 20	155/75	Lifetime	Integrated	N/A	N/A	8"	11¾"	8"	23 lbs
F715	Napoli™ II	111	68"	5	14°	212 x 25	110/50	Lifetime	Integrated	3½" & 12"	N/A	80"	16¼"	10"	46 lbs
F726	Spectre	12-15	60"	4	14°	DC188 x 10	120/50	Lifetime	Integrated	3½" & 6"	N/A	80"	14½"	11"	22 lbs
F733	Gilera	48-51	62"	3	14°	212 x 25	100/45	Lifetime	N/A	3½" & 6"	N/A	80"	14"	14½"	35 lbs
F734	Strata	138-139	52"	4	12°	172 x 17	153/60	Lifetime	Integrated	3½" & 6"	N/A	80"	15"	13"	19 lbs
F737	Moda	60-61	60"	3	20°	DC188 x 14	152/53	Lifetime	N/A	3½" & 6"	N/A	80"	12"	12½"	35 lbs
F738	Pancake	52-53	52"	4	12°	153 x 18	180/70	Lifetime	N/A	6"	N/A	12"	9¾"	8¾"	19 lbs
F745	Sabot	24-25	52"	5	12°	DC172 x 12	150/65	Lifetime	Integrated	3½" & 6"	N/A	80"	9½"	7¾"	19 lbs
F753	Java	68-69	54"	3	14°	153 x 18	169/75	Lifetime	N/A	3½" & 6"	N/A	80"	12½"	11½"	19 lbs
F759	Classica Gallery Edition	188	54"	5	14°	172 x 16	187/63	Lifetime	Adaptable	3½" & 6"	N/A	80"	18¼"	10½"	26 lbs
F802	Vintage Gyro™	116-117	42"	6	20°	82 x 25	1360/720	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	18½"	28 lbs
F803	Artemis™	34-39	58"	3	Variable	188 x 25	135/75	Lifetime	Integrated	3½" & 6"	N/A	80"	13"	11½"	25 lbs
F812	Lineage™	107	54"	5	14°	188 x 25	144/81	Lifetime	Integrated	3½" & 6"	N/A	80"	13½"	12½"	40 lbs
F820	Santa Lucia™	106	60"	5	14°	188 x 25	146/70	Lifetime	Integrated	3½" & 6"	N/A	80"	18"	13¼"	39 lbs
F823	Wing	40-43	52"	1	Variable	DC125 x 30	150/50	Lifetime	N/A	6"	N/A	80"	10¾"	10"	11 lbs
F824	Uchiwa	76-77	56"	3	20°	172 x 25	130/70	Lifetime	Integrated	3½" & 6"	N/A	80"	18¼"	10¼"	26 lbs
F828	Symbio	26-27	60"	5	13°	DC125 x 30	150/50	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	13¼"	25 lbs
F833	Kewl	58-59	52"	3	22°	153 x 15	201/46	Lifetime	N/A	3½" & 6"	N/A	80"	11"	8¾"	19 lbs
F840	Craftsman™	128	52"	5	14°	172 x 20	180/75	Lifetime	Included	3½" & 6"	N/A	80"	21¼"	13¼"	31 lbs
F843	Wave	46-47	52"	3	48°	172 x 14	153/61	Lifetime	N/A	4½" & 6"	N/A	80"	13"	9½"	19 lbs
F844	Light Wave	44-45	52"	3	48°	172 x 14	139/57	Lifetime	Integrated	4½" & 6"	N/A	80"	13½"	11½"	20 lbs
F853	Aviation	28-31	60"	3	Variable	DC120 x 25	115/44	Lifetime	N/A	3½" & 6"	N/A	80"	12"	10½"	19 lbs
F887	Xtreme	16-21	88"	9	4°	DC165 x 12	80/50	Lifetime	N/A	3½" & 6"	N/A	80"	15"	13½"	50 lbs
F888	Slipstream	32-33	65"	8	14°	DC165 x 25	98/50	Lifetime	Integrated	3½" & 6"	N/A	80"	14"	11½"	35 lbs
F889	Slipstream XXL	132-137	84"	8	14°	DC165 x 25	90/50	Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	10¼"	45 lbs
F900	Cristafano™	109	68"	5	14°	212 x 25	112/52	Lifetime	Integrated	3½" & 6"	N/A	80"	14"	13"	29 lbs
F905	Artemis™ XL5	56-57	62"	5	28°	DC172 x 25	91/50	Lifetime	Integrated	3½" & 6"	N/A	80"	16½"	13¾"	35 lbs
F1000	Dyno	164-165	52"	5	14°	153 x 17	170/62	Lifetime	Integrated	3½" & 6"	N/A	80"	12"	10¼"	19 lbs

* Dimensions A & B were measured with the shortest downrod enclosed with the fan (See the Finish Codes page for Picture Diagrams)

** F601 dimensions A & B were measured without light kit



*** All Conventional Motors are 16 Poles

Finish Codes


Minka-Aire® / Minka-Lavery® Finish Compatibility Chart

Minka-Lavery®	Minka-Aire®
	AB Antique Brass
	ABD Brushed Aluminum
126	BCW Belcaro Walnut™
	BG Bahama Beige™
	BI/AI Black Iron with Aged Iron Accents
66	BK Black
84	BN Brushed Nickel
	BNW Brushed Nickel Wet
	BS Brushed Steel
	BWH Bone White
	CC Cognac
	CF Craftsman™
77	CH Chrome
	CPBR Copper Bronze
	CT Cattera Bronze™
267C	DBB Dark Brushed Bronze
	DK Distressed Koa
	DKG Distressed Koa with Gold Highlights
37B	DRB Dark Restoration Bronze™
	DRF Driftwood
	FB French Beige
477	FLP Florence Patina™
355	GBZ Golden Bronze
	GL Galvanized
	GM Gun Metal
94	HT Heritage™
177	IBR Illuminati Bronze™
357	IO Iron Oxide
	KA Kocoa
	LN Liquid Nickel
	MBK Matte Black
	MCG Mottled Copper with Gold Highlights
	MG Mahogany Finish
	MP Maple Finish
	MW Mossoro Walnut™
	ODK Outdoor Distress Koa
143	ORB Oil Rubbed Bronze
	ORG Orange
648	PBL Provencal Blanc
573	PI Patina Iron
613	PN Polished Nickel
	PW Pewter
	RD Red
37	RRB Restoration Bronze™
	RW Rosewood
172	SI Smoked Iron
	SL Silver
	STW Sterling Walnut™
	SWH Shell White
	TB Toned Brass
	TL Translucent
196C	TSP Tuscan Patina™
	VB Volterra Bronze™
	VP Vineyard Patina
61	VRT Vintage Rust™
44	WH White
	WHF Flat White
	YW Yellow

Dimensions A and B were measured with the shortest downrod enclosed with the fan.



Minka-Aire® ceiling fans are suitable for year-round use and can contribute to your comfort in the summer and winter. With our reverse switch, in the winter you will be able to move the heat from your ceiling and circulate the air in your living area. In the summer you will save energy by recirculating air from the outside into your room and also if your air conditioning is used, save on energy costs.



We Support



Member



Graphic Design: Minka Group® Graphics
Product Originals: Minka Group®

Product specifications subject to change at any time.

Minka-Aire®, A Minka Group® Company
Catalog MKACAT2015-04
Printed in U.S.A.
© 1993-2015 Minka Lighting, Inc.