



# Westinghouse

INNOVATION YOU CAN BE SURE OF

LIGHTING



FANS



Westinghouse Lighting Latin America  
Catalog 2014





# Westinghouse

INNOVATION YOU CAN BE SURE OF



WESTINGHOUSE HAS BEEN  
A TRUSTED BRAND FOR GENERATIONS

<b>Contacts</b>	4
<b>Fan Collection</b>	5
Ceiling Fan	6
Ceiling Fan Specifications	37
Ceiling Fan Accessories	43
Portable Fans	51
<b>Lighting Fixtures Collection</b>	60
Indoor Ceiling Lighting Fixtures	61
Set of Lighting Fixtures	70
Indoor Wall Lighting Fixtures	73
Lighting Fixture Pendants	77
Ceiling Reflectors	79
Fixed Down Lights	81
Desk Lighting Fixtures	85
Outdoor Ceiling Lighting Fixtures	87
Outdoor Wall Lighting Fixtures	89
Lighting Fixture Accessories	96
<b>Electrical Devices</b>	104
<b>Light Bulbs</b>	106
Fluorescent Light Bulbs	107
LED Light Bulbs	114
Incandescent Light Bulbs	117
Halogen Light Bulbs	122
<b>Fans and Lighting Fixtures Finishes</b>	125
<b>Index &amp; Cubic Capacity</b>	128

# CONTACTS

## Panama

Showroom & Distribution Center  
Westinghouse Lighting Latin America  
Avenue 4th, Calle 5th Street  
France Field, Colon Free Zone, Panama  
Phone/Fax: (507) 430-1737  
E-mail: ventas1@wl-la.com

## Mexico

Westinghouse Lighting Mexico  
Insurgentes Sur, No. 813, Mezzanine 1  
Col. Napoles Del. Benito Juarez C.P. 03810,  
Mexico D.F. Mexico,  
Phone: 52-55-5687-1896  
Fax: 52-55-5682-5683

## Colombia

Phone.: (57) 1610-3720  
Fax: (57) 1610-1839

## Miami

Phone.: (001) 786-242-7935  
Fax: (001) 786-288-0339

## El Salvador

Phone.: (503) 2264-4780  
Fax: (503) 2263-7383

## Dominican Republic

Phone.: (809) 473-6151/6202  
Fax: (809) 473-6992

## Nicaragua

Phone.: (505) 266-9813  
Fax: (505) 268-4242

## Costa Rica

Phone.: (506) 2443-5715  
Cel: (506) 8910-1616

## Peru

Phone.: (51) 994-62-66-15

## OTHER COUNTRIES

- |                          |                                |
|--------------------------|--------------------------------|
| » Anguilla               | » Montserrat                   |
| » Antigua & Barbuda      | » St. Barts                    |
| » Aruba                  | » St. Kitts & Nevis            |
| » Barbados               | » St. Lucia                    |
| » Bonaire                | » St. Maarten                  |
| » British Virgin Islands | » St. Vincent & the Grenadines |
| » Cayman Islands         | » Trinidad & Tobago            |
| » Curaçao                | » Turks & Caicos               |
| » Dominica               | » US Virgin Islands            |
| » Grenada                |                                |
| » Guadeloupe             |                                |
| » Martinique             |                                |







# CEILING FANS COLLECTION


Products Available in 120 V- / 220 V-, 50 Hz / 60 Hz






CEILING  
FAN  
BENEFITS

## CEILING FANS FOR ALL YEAR





*SUMMER*



*WINTER*


With a switch that allows the blades to rotate clockwise or counterclockwise.

## CEILING FAN MOUNTINGS





## CEILING FANS APPLICATIONS



For use in rooms up to 8'x10'  
Ceiling Fans 24" - 42"  
(Small Size Bedrooms, walk-in closets, kitchens)

For use in rooms up to 12'x12'  
Ceiling Fans 42" - 48"  
(Medium Bedrooms, kitchens, and small recreations areas)

For use in rooms up to 18'x20'  
Ceiling Fans 52" - 56"  
(Big Size Bed Rooms, living rooms, Big Size Rooms, Low Ceiling Dining Room)

## INDOOR AND OUTDOOR CEILING FANS



## CERTIFICATES



## SILENT CEILING FANS

- No air spaces between parts
- Rubber washers between parts to avoid vibrations
- Rubber washers assembled in the union plateto reduce vibrations in the ceiling
- Sealed and lubricated by manufacturer
- Triple capacitor - reduce volts to motor and speed control



CONTEMPORARY






**72559** NEW  
**PANORAMA**  
 132 cm / 52"



- Chrome Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Black White

**78685**  
**CELESTIA II**  
 122 cm / 48"



Included

- Brushed Aluminum Finish
- 3 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)
- Remote Control Included

Finished Blades



Graphite

**78556**  
**JEWEL**  
 132 cm / 52"



- Chrome Finish
- 5 MDF Blades
- Lighting Fixture
- White Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)

Finished Blades



White

**78293**  
**JEWEL**  
 132 cm / 52"



- Chrome Finish
- 5 MDF Blades
- Lighting Fixture
- Cobalt Blue Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)

Finished Blades



Cobalt Blue






**78992** NEW  
**COMET**  
132 cm / 52"



- Brushed Nickel Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Light Maple Espresso


**78181** NEW  
**COMET**  
132 cm / 52"



Included

- Brushed Nickel Finish
- 5 Plywood Blades
- Lighting Fixture
- Vidrio Tipo Ópalo en Acabado Esmerilado
- (2) Light Bulbs Standard Base (Not Included)
- Remote Control Included

Finished Reversible  
Blades




Light Maple Wengue

**78016**  
**COMET**  
132 cm / 52"



- Black Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Black Marble Black

**78017**  
**COMET**  
132 cm / 52"



- White Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



White Washed Pine White




**78136**  
COMET  
132 cm / 52"



- Brushed Pewter Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Light Maple White

**78611**  
COMET  
132 cm / 52"



- Brushed Nickel Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Light Maple Rosewood

**78009**  
COMET  
132 cm / 52"



- Iron Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Rosewood Walnut

**72384**  
COMET  
132 cm / 52"



- Rustic Bronze Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Rich Walnut Mahogany




**78993** NEW  
**COMET**  
132 cm / 52"



- White Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Blue Pink

**78712**  
**COMET**  
132 cm / 52"



- Old Chicago Finish
- 5 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Walnut Distressed  
Pine

**72141**  
**HARMONY**  
122 cm / 48"



- Brushed Nickel Finish
- 2 Plywood Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Blades




Weathered Maple

**78569**  
**EURO SWIRL**  
132 cm / 52"



- Iron Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Rosewood Walnut




**78612**  
EURO SWIRL  
132 cm / 52"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



White Washed Pine    White

**72390**  
EURO SWIRL  
132 cm / 52"



- Brushed Nickel Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Light Maple    Rosewood

**78209**  
EURO SWIRL  
132 cm / 52"



- Titanium Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Light Maple    White

**78583**  
EURO SWIRL  
132 cm / 52"



- Rustic Bronze Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Rich Walnut    Mahogany



**72502** NEW  
**TURBO MAX**  
106 cm / 42"



- Espresso Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**72517**  
**TURBO MAX**  
106 cm / 42"



- White Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**78767** NEW  
**PARADISE**  
122 cm / 48"




- Ebony Bronze Finish
- 4 Blades
- Lighting Fixture
- Frosted Opal Glass
- (3) Light Bulbs Standard Base (Not Included)



**72386**  
**TURBO SWIRL**  
76 cm / 30"



- Rustic Bronze Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)







**78713** NEW  
**TURBO SWIRL**  
 76 cm / 30"



- Burnished Bronze Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**78023**  
**TURBO SWIRL**  
 76 cm / 30"



- Iron Finish
- 6 Aspas de MDF
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**78248**  
**TURBO SWIRL**  
 76 cm / 30"




- Antique Brass Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**72387**  
**TURBO SWIRL**  
 76 cm / 30"



- Washed Copper Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)







**78145**  
TURBO SWIRL  
76 cm / 30"



- White Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**72503** NEW  
TURBO SWIRL  
76 cm / 30"



- Brushed Nickel Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**78629**  
TURBO SWIRL  
76 cm / 30"



- Brushed Nickel Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**78144**  
TURBO SWIRL  
76 cm / 30"



- Brushed Aluminum Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)





**72186** NEW  
**TURBO SWIRL CFL**  
 76 cm / 30"



- Satin Chrome Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**72156** NEW  
**TURBO SWIRL II**  
 76 cm / 30"




- Brushed Nickel Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**78673**  
**TURBO SWIRL II**  
**MULTICOLOR**  
 76 cm / 30"




- White Finish
- 2 Sets of 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)



**78676** NEW  
**TURBO SWIRL II**  
**KIDS**  
 76 cm / 30"



- White Finish
- 6 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (1) Light Bulb Standard Base (Not Included)





TRADITIONAL

...




**72152** NEW  
**EVERETT**  
 132 cm / 52"



- Brushed Nickel Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Opal Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
 Blades



Beech Wengue


**78400** NEW  
**FAIRVIEW**  
 132 cm / 52"



Included

- Brushed Nickel Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)
- Remote Control Included

Finished Reversible  
 Blades




Dark cherry Degraded Maple

**78724** NEW  
**ORION**  
 132 cm / 52"



- Oil Rubbed Bronze Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
 Blades




Beech Degraded Maple

**78799**  
**BETHANY**  
 132 cm / 52"



- Rustic Bronze Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
 Blades



Rich Walnut Mahogany






**78677**  
**BETHANY**  
132 cm / 52"



- Brushed Pewter Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Light Maple      White

**78610**  
**BETHANY**  
132 cm / 52"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




White Washed  
Pine      White

**78112**  
**IMPERIAL**  
132 cm / 52"



- Antique Brass Finish
- 5 MDF Blades
- Lighting Fixture
- Clear & Frosted Tulip Glass
- (5) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



High Gloss  
Maple      High  
Gloss  
Walnut

**78711** NEW  
**CANES**  
132 cm / 52"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Pine      White




**78613**  
VINTAGE  
132 cm / 52"



- Washed Copper Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Rosewood Walnut

**78627**  
VINTAGE  
132 cm / 52"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




White Washed  
Pine White

**72389**  
VINTAGE  
132 cm / 52"



- Iron Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Rosewood Walnut

**78434**  
VINTAGE  
132 cm / 52"



- Old Chicago Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Walnut Distressed  
Pine






**78433**  
**VINTAGE**  
132 cm / 52"



- Brushed Pewter Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Light Maple      White

**78678**  
**VINTAGE**  
132 cm / 52"



- Brushed Nickel Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Light Maple      Rosewood

**78042**  
**VINTAGE**  
132 cm / 52"



- Antique Brass Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Oak      Walnut

**78568**  
**SWIRL**  
132 cm / 52"



- Rustic Bronze Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Rich Walnut      Mahogany




**78079**  
SWIRL  
132 cm / 52"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




White Washed  
Pine      White

**78521**  
SWIRL  
132 cm / 52"



- Brushed Nickel Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Light Maple      Rosewood

**78567**  
SWIRL  
132 cm / 52"




- Iron Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Rosewood      Walnut

**78432**  
SWIRL  
132 cm / 52"



- Old Chicago Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Walnut      Distressed  
Pine

**78374**  
VINTAGE II  
132 cm / 52"



- Oil Rubbed Bronze Finish
- 5 MDF Blades
- Lighting Fixture
- Alabaster Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Dark  
Cherry      Walnut

**78391**  
VINTAGE II  
132 cm / 52"



- Brushed Nickel Finish
- 5 MDF Blades
- Lighting Fixture
- Alabaster Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Light  
Maple      Rosewood

**72392**  
VINTAGE II  
132 cm / 52"



- Antique Brass Finish
- 5 MDF Blades
- Lighting Fixture
- Alabaster Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Oak      Walnut

**78314**  
VINTAGE II  
132 cm / 52"



- Rustic Bronze Finish
- 5 MDF Blades
- Lighting Fixture
- Alabaster Bowl Glass
- (2) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Rich  
Walnut      Mahogany



**78024**  
**CONTRACTOR'S CHOICE**  
 132 cm / 52"



- White Finish
- 5 ABS Blades
- Optional Lighting Fixture



**78714**  
**CONTEMPRA IV**  
 132 cm / 52"



- Antique Brass Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (4) Light Bulbs Standard Base (Not Included)



**78772**  
**RICHBORO SE**  
 106 cm / 42"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- Alabaster Bowl Glass
- (2) Light Bulbs E12 Base (Not Included)



**78268**  
**RICHBORO SE**  
 106 cm / 42"



- Antique Brass Finish
- 5 MDF Blades
- Lighting Fixture
- Alabaster Bowl Glass
- (2) Light Bulbs E12 Base (Not Included)






**78133**  
PRINCESS AMBIANCE  
106 cm / 42"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- White Mushroom Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades




White Washed  
Pine      White

**78449**  
PORTLAND AMBIANCE  
106 cm / 42"



- Antique Brass Finish
- 5 MDF Blades
- Lighting Fixture
- White Mushroom Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades



Oak      Walnut

**78508**  
CONTEMPRA TRIO  
106 cm / 42"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




White Washed  
Pine      White

**78615**  
CONTEMPRA TRIO  
106 cm / 42"



- Brushed Nickel Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades



Bird's  
Eye Maple      Rosewood





**78126**  
CASANOVA SUPREME  
106 cm / 42"



- White Finish
- 4 MDF Blades
- Lighting Fixture
- White School House Finish
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades




White Washed Pine    White

**78123**  
CASANOVA SUPREME  
106 cm / 42"



- Antique Brass Finish
- 4 MDF Blades
- Lighting Fixture
- White School House Finish
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades




Oak    Walnut

**78146**  
CRUSADER  
106 cm / 42"



- Antique Brass Finish
- 4 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Oak    Walnut

**72414** NEW  
PRINCESS RADIANCE  
76 cm / 30"



- Chrome & Dark Pewter Finish
- 5 MDF Blades
- Lighting Fixture
- White Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades



White    Wengue






**78671** NEW  
EOLO  
91 cm / 36"



- Brushed Nickel Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Light Maple      Rosewood

**78669** NEW  
EOLO  
91 cm / 36"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- Frosted Tulip Glass
- (3) Light Bulbs Standard Base (Not Included)

Finished Reversible  
Blades




Washed Oak      White

**78658** NEW  
ZEFIRO  
91 cm / 36"



- Antique Brass Finish
- 5 MDF Blades
- Lighting Fixture
- White Opal Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades




Oak      Walnut

**78657** NEW  
ZEFIRO  
91 cm / 36"



- White Finish
- 5 MDF Blades
- Lighting Fixture
- White Opal Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades



Washed Oak      White




**78108**  
**PETITE**  
 76 cm / 30"



- White Finish
- 6 MDF Blades
- Lighting Fixture
- White Mushroom Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades




White Washed Pine    White

**72394**  
**PETITE**  
 76 cm / 30"



- Brushed Nickel Finish
- 6 MDF Blades
- Lighting Fixture
- White Mushroom Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades




Light Maple    Rosewood

**72395**  
**PETITE**  
 76 cm / 30"



- Rustic Bronze Finish
- 6 MDF Blades
- Lighting Fixture
- White Mushroom Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades




Rich Walnut    Mahogany

**78170**  
**SOCCER FAN**  
 76 cm / 30"



- White Finish
- 6 MDF Blades
- Lighting Fixture
- White Mushroom Glass
- (1) Light Bulb Standard Base (Not Included)

Finished Reversible  
Blades



White    Soccer Sticker



INDUSTRIAL

...



**78614**  
INDUSTRIAL  
142 cm / 56"



Included


- Brushed Nickel Finish
- 3 Metal Blades
- Motor 153 x 17 mm
- Wall Control 5 Speeds Included

Finished Blades



Brushed Nickel

**72175**  
INDUSTRIAL  
142 cm / 56"



Included

- Antique Copper Finish
- 3 Metal Blades
- Motor 153 x 17 mm
- Wall Control 5 Speeds Included

Finished Blades



Antique Copper

**72174**  
INDUSTRIAL  
142 cm / 56"



Included

- Antique Brass Finish
- 3 Metal Blades
- Motor 153 x 12.8 mm
- Wall Control 5 Speeds Included

Finished Blades



Antique Brass

**78623**  
INDUSTRIAL  
142 cm / 56"



Included

- Espresso Finish
- 3 Metal Blades
- Motor 170.3 x 12.8 mm
- Wall Control 5 Speeds Included

Finished Blades



Espresso



### 72401 INDUSTRIAL REBEL 142 cm / 56"



### 72399 INDUSTRIAL 142 cm / 56"



### 78127 INDUSTRIAL 142 cm / 56"



### 72400 PERFORMANCE PLUS 142 cm / 56"







**78680**  
INDUSTRIAL  
142 cm / 56"



Included



- Acabado White
- 3 Metal Blades
- Motor 153 x 17 mm
- Wall Control 5 Speeds Included with Switch
- Optional Lighting Fixture (Not Included)



White


**72558** NEW  
INDUSTRIAL  
142 cm / 56"



Included



- Chrome Finish
- 3 Metal Blades
- Motor 153 x 17 mm
- Wall Control 5 Speeds Included with Switch
- Optional Lighting Fixture (Not Included)



Chrome



INDOOR & OUTDOOR

...





**72281**  
WILLOW BREEZE  
132 cm / 52"



- Espresso Finish
- 5 ABS Resin Blades
- Lighting Fixture Optional



**72280**  
WILLOW BREEZE  
132 cm / 52"



- White Finish
- 5 ABS Resin Blades
- Lighting Fixture Optional





## CEILING FAN SPECIFICATIONS

...



## CEILING FAN SPECIFICATIONS

	Size	Fan Mounting	Blades Number	Blades Pitch	Motor Size (mm)	Capacitor Type	Capacitor	Capacitor Item Number	Replacement Glass Item Number
<b>Bethany</b>	52"	Combo	5	11°	153 x 15 C.R.S.	Triple	4.5+5+5uf	78960	78984
<b>Bethany (78799)</b>	52"	Combo	5	11°	153 x 15 C.R.S.	Triple	4.5+5+5uf	78960	78836
<b>Canes</b>	52"	Combo	5	10.5°	153 x 12 C.R.S.	Triple	6+6+4.2uf	---	---
<b>Casanova Supreme</b>	42"	Hugger	4	12°	153 x 10 C.R.S.	Dual	1.25+2.25uf	78934	86902
<b>Celestia II</b>	48"	Hugger	3	12°	153 x 15 S.S.	Single	4.5uf	---	---
<b>Comet</b>	52"	Combo	5	11°	153 x 15 C.R.S.	Triple	4.5+5+5uf	78960	78890
<b>Contempra IV</b>	52"	Hugger	5	11°	153 x 15 C.R.S.	Triple	4.5+5+5uf	78960	86901
<b>Contempra Trio</b>	42"	Hugger	5	12°	153 x 10 C.R.S.	Dual	1.25+2.25uf	78934	65221
<b>Contractors Choice</b>	52"	Combo	5	12°	153 x 13 C.R.S.	Triple	4.5+4+5uf	---	---
<b>Crusader</b>	42"	Combo	4	12°	153 x 10 C.R.S.	Dual	1.25+2.25uf	78934	79315
<b>Eolo</b>	36"	Hugger	5	14°	153 x 8 C.R.S.	Dual	1.3+2.5uf	---	---
<b>Euro Swirl</b>	52"	Combo	5	11°	153 x 15 C.R.S.	Triple	4.5+5+6uf	78959	65222
<b>Everett</b>	52"	Hugger	5	12°	153 x 15	Triple	4.5+5+6uf	78959	---
<b>Fairview</b>	52"	Combo	5	12°	153 x 12 C.R.S.	Dual	---	---	---
<b>Harmony</b>	48"	Down Rod Only	2	13°	153 x 20	Triple	5+3+4uf	---	---
<b>Imperial</b>	52"	Combo	6	11°	153 x 15 C.R.S.	Triple	4.5+5+5uf	78960	781126910
<b>Industrial (78127)</b>	56"	Down Rod	3	8°	153 x 17 C.R.S.	Single	3.75uf	78962	----
<b>Industrial (72399)</b>	56"	Down Rod	3	7°	170.3 x 12.8 C.R.S.	Single	4.5uf	----	----
<b>Industrial (72400)</b>	56"	Down Rod	3	8°	170.3 x 19.2 C.R.S.	Single	4.5uf	----	----
<b>Industrial Rebel (72401)</b>	56"	Down Rod	3	7°	153 x 12.8 C.R.S.	Single	4.5uf	----	----

S.S.- Silicon Steel


C.R.S.- Cold Rolled Steel

\* Specifications can be changed



	Down Road	Blade Material	Remote Control Adaptable	CFM (High)	RPM (Low-High)	Watts (High)	Amps (High)	A	B	C	D	E	F
Bethany	1/2" x 4"	MDF	Si	4978	65-175	63	0.52	10 1/4"	12 5/8"	2 3/8"	12 1/8"	5 1/8"	17 1/4"
Bethany (78799)	1/2" x 4"	MDF	Si	4978	65-175	63	0.52	10 1/4"	12 5/8"	2 3/8"	12 1/8"	5 1/8"	17 1/4"
Canes	3/4" x 4"	MDF	Si	4500	130-230	60	0.50	13"	13 5/8"	2 2/4"	11 1/8"	5 1/8"	17 3/4"
Casanova Supreme	N/A	MDF	No	4410	110-220	56	0.45	7 1/4"	8 1/2"	N/A	8 3/4"	N/A	12 1/2"
Celestia II	N/A	MDF	Includo	4225	106-216	47	0.40	9 1/5"	10 2/5"	4 2/3"	10"	5 3/5"	13 3/4"
Comet	1/2" x 4"	Plywood	Si	5098	84-180	60	0.50	11 7/8"	14 1/4"	2 1/4"	11 1/2"	5 1/8"	14 1/4"
Contempra IV	N/A	MDF	Si	4978	65-175	63	0.52	7 1/8"	8 1/8"	N/A	11 1/2"	N/A	13"
Contempra Trio	N/A	MDF	No	4410	110-210	54	0.45	5 3/4"	8"	N/A	11 1/4"	N/A	13 3/8"
Contractors Choice	3/4" x 4"	MDF	Si	4839	86-182	64	0.52	11"	13"	2 1/2"	11"	5"	N/A
Crusader	1/2" x 4"	MDF	Si	4410	110-220	56	0.45	9 7/8"	14"	2 1/8"	8 1/4"	5 1/8"	18 1/2"
Eolo	N/A	MDF	No	3500	90-170	40	0.33	6 1/5"	8"	4 2/5"	8 3/5"	N/A	12 4/5"
Euro Swirl	1/2 x 4"	MDF	Si	4978	65-175	63	0.52	10 1/4"	12 1/2"	2 1/4"	11 1/2"	5 1/8"	16"
Everett	N/A	MDF	No	4920	71-181	62	0.52	7 7/8"	7"	4 1/3"	11 3/7"	N/A	12 3/5"
Fairview	---	MDF		4370	75-170	58	0.49	30"	33"	6 1/3"	28"	13"	44 7/8"
Harmony	3/4" x 6"	Plywood	Si	4881	95-210	52	0.46	10 5/8"	12 3/4"	2"	7 1/2"	6"	17 1/8"
Imperial	1/2" x 4"	MDF	Si	5098	84-180	60	0.50	13"	13 1/4"	2 1/4"	12 3/4"	5 1/4"	20 1/4"
Industrial (78127)	1/2" x 12"	Steel	No	5098	84-180	60	0.50	13"	13 1/4"	2 1/4"	12 3/4"	5 1/4"	20 1/4"
Industrial (72399)	1/2" x 12"	Steel	No	5098	84-180	60	0.50	13"	13 1/4"	2 1/4"	12 3/4"	5 1/4"	20 1/4"
Industrial (72400)	1/2" x 12"	Metal	No	7592	145-260	68	0.57	14 9/16"	17 11/16"	2 3/8"	8 7/8"	5 1/8"	N/A
Industrial Rebel (72401)	1/2" x 12"	Metal	No	6886	125-255	61	0.50	14 9/16"	17 11/16"	2 3/8"	8 7/8"	5 1/8"	N/A

If a Combo Style Fan is Installed Without a Dwn Rod, Subtract 3" from the Dimension Listed (a, b, f).



- A - Top of Canopy to Bottom of Blade
- B - Top of Canopy to Bottom of Switch Housing
- C - Top of Canopy to Bottom of Canopy
- D - Width of Motor Housing
- E - Width of Canopy
- F - Top of Canopy to Bottom of Glass

## CEILING FAN SPECIFICATIONS

	Size	Fan Mounting	Blades Number	Blades Pitch	Motor Size (mm)	Capacitor Type	Capacitor	Capacitor Item Number	Replacement Glass Item Number
<b>Jewel (78293)</b>	52"	Combo	5	11°	153 x 15 S.S.	Triple	4.5+5+5uf	78960	78803
<b>Jewel (78556)</b>	52"	Combo	5	11°	153 x 15 S.S.	Triple	4.5+5+5uf	78960	78829
<b>Orion</b>	52"	Combo	5	10.5°	153 x 12 C.R.S.	Triple	(6+6uf)(4.2uf)	----	----
<b>Panorama</b>	52"	Combo	5	12°	153 x 17	Triple	----	----	----
<b>Paradise</b>	48"	Combo	4	11°	144 x 14	Dual	----	----	----
<b>Petite</b>	30"	Hugger	6	18°	153 x 9 C.R.S.	Dual	1+2uf	78930	86427
<b>Portland Ambiance</b>	42"	Combo	4	12°	145 x 12 C.R.S.	Dual	1.5+3uf	----	86427
<b>Princess Ambiance</b>	42"	Combo	4	12°	153 x 10 C.R.S.	Triple	3.5+4+4uf	78932	86427
<b>Princess Radiance</b>	30"	---	4	12°	153 x 10	Triple	----	----	----
<b>Radiance</b>	56"	Down Rod	3	7°	170.3 x 12.8 C.R.S.	Single	5uf	----	----
<b>Richboro SE</b>	42"	Combo	5	12°	153 x 8 S.S.	Dual	2+4uf	78772/CA	787726910
<b>Swirl</b>	52"	Combo	5	11°	153 x 15 C.R.S.	Triple	4.5+5+6uf	78959	78915
<b>Soccer Fan</b>	30"	Hugger	6	18°	153 x 9 C.R.S.	Dual	1+2uf	78930	----
<b>Turbo Max</b>	42"	Combo	6	12°	172 x 16 C.R.S.	Dual	2+4uf	78772/CA	78891
<b>Turbo Swirl</b>	30"	Combo	6	18°	153 x 10 C.R.S.	Dual	1.25+2.5uf	78927	78891
<b>Turbo Swirl II</b>	30"	Combo	6	18°	153 x 10	----	1.25+2.5uf	78927	---
<b>Turbo Swirl CFL</b>	30"	Combo	6	18°	153 x 12	Dual	1.5+2.5uf	----	----
<b>Turbo Swirl II Kids</b>	30"	Combo	6	18°	153 x 10	Dual	1.5+2.5uf	----	----
<b>Vintage</b>	52"	Combo	5	11°	153 x 15 C.R.S.	Triple	4.5+5+5uf	78960	86901
<b>Vintage II</b>	52"	Combo	5	11°	153 x 12 C.R.S.	Triple	4.5+5+5uf	78960	78984
<b>Willow Breeze</b>	52"	Combo	5	11°	153 x 15 S.S.	Triple	3.75+4.5+6uf	----	78990
<b>Zefiro</b>	36"	Hugger	5	14°	153 x 8 C.R.S.	Dual	1.3+2.5uf	----	----

S.S.- Silicon Steel

C.R.S.- Cold Rolled Steel

\* Specifications can be changed

	Down Road	Blade Material	Remote Control Adaptable	CFM (High)	RPM (Low-High)	Watts (High)	Amps (High)	A	B	C	D	E	F
<b>Jewel (78293)</b>	3/4" x 4"	MDF	Si	4,978	87-174	63	0.52	10 1/4"	13 3/4"	2 1/8"	11 1/2"	5 1/8"	21 1/4"
<b>Jewel (78556)</b>	3/4" x 4"	MDF	Si	4,978	87-174	63	0.52	10 1/4"	13 3/4"	2 1/8"	11 1/2"	5 1/8"	21 1/4"
<b>Orion</b>	3/4" x 4"	MDF	Si	4,500	130-230	60	0.50	13"	14 2/5"	2 2/5"	12 2/5"	4 4/5"	18 3/5"
<b>Panorama</b>	----	MDF	Si	4,733	---	63	0.53	31"	22"	6"	27"	13"	40"
<b>Paradise</b>	3/4" x 4"	MDF	Si	----	----	----	----	----	----	----	----	----	----
<b>Petite</b>	N/A	MDF	No	3,925	130-260	45	0.36	6 3/4"	8"	N/A	9"	N/A	12"
<b>Portland Ambiance</b>	1/2" x 4"	MDF	Si	3,925	95-230	45	0.20	18"	31"	5"	17"	13"	44"
<b>Princess Ambiance</b>	1/2" x 4"	MDF	Si	3,925	130-260	45	0.36	12 1/4"	12 1/2"	2 1/8"	6 5/8"	5 1/4"	16 7/8"
<b>Princess Radiance</b>	----	MDF	Si	----	----	45	0.36	72	81	15	43	33	112
<b>Radiance</b>	1/2" x 6"	Metal	No	741,615	120-260	68	0.57	9"	13 1/2"	2 3/8"	9 1/2"	5 1/8"	15 1/4"
<b>Richboro SE</b>	1/2" x 4"	MDF	Si	4,280	65-190	51	0.42	11 2/3"	13"	2 1/4"	8 1/4"	5 1/8"	17 1/2"
<b>Swirl</b>	1/2" x 4"	MDF	Si	5,098	84-180	60	0.50	13 1/2"	12"	2 1/4"	12"	5 1/4"	18"
<b>Soccer Fan</b>	N/A	MDF	No	3,925	130-260	45	0.36	6 3/4"	8"	N/A	9"	N/A	12"
<b>Turbo Max</b>	3/4" x 4"	MDF	Si	4,410	105-215	50	0.42	11 7/8"	11 3/8"	2 1/2"	6 3/4"	5 1/8"	14 1/4"
<b>Turbo Swirl</b>	1/2" x 4"	MDF	Si	3,925	130-260	45	0.36	10"	11 1/2"	2 1/4"	7"	5"	14 1/2"
<b>Turbo Swirl II</b>	----	MDF	Si	----	---	50	0.36	8 5/8"	11 5/8"	2 1/4"	6 3/4"	5 1/8"	16 3/4"
<b>Turbo Swirl CFL</b>	3/4" x 4"	MDF	Si	3,519	130-260	50	0.42	8 5/8"	11 5/8"	2 1/4"	6 3/4"	5 1/8"	16 3/4"
<b>Turbo Swirl II Kids</b>	3/4" x 4"	MDF	Si	3,519	130-260	50	0.42	10"	12"	2 3/5"	7"	5 2/5"	15"
<b>Vintage</b>	1/2" x 4"	MDF	Si	5,098	84-180	60	0.50	11"	12 1/4"	2 1/4"	11"	5"	18 1/4"
<b>Vintage II</b>	3/4" x 4"	MDF	Si	4,850	75-170	65	0.53	11 3/8"	13 1/4"	2 3/8"	11 1/8"	5 1/8"	19 1/4"
<b>Willow Breeze</b>	1/2" x 4"	ABS Resin	Si	4,978	65-175	63	0.52	8 3/4"	11 5/8"	2 1/4"	10 1/4"	5 1/8"	16 1/2"
<b>Zefiro</b>	N/A	MDF	No	3,500	90-170	10	0.08	7 2/5"	8"	4 2/5"	8 3/5"	N/A	12"


# CEILING FAN DISPLAY

## 96206

- 4' Canopy Extension Ceiling Fan Display
- Westinghouse Header
- Hardware Included
- Easy Assembly and Installation
- No Electrical Hook-up Needed
- Displays up to 3 Ceiling Fans



\*Product not included





## CEILING FAN ACCESSORIES

...



## 77871 WALL CONTROL

- For Fan Without Light
- 4 Speeds  
(High/Medium High/Medium Low/Low)
- Turn Any Fan of 3 Speeds Into a 4 Speeds Fan
- Replace the Switch
- 120 V- 60 Hz Amp. Max. 1.25
- Master Carton: 32
- Inner Pack: 4



## 77872 WALL CONTROL

- For Fan Without Light
- 4 Speeds  
(High/Medium High/Medium Low/Low)
- Turn Any Fan of 3 Speeds Into a 4 Speeds Fan
- Replace the Switch
- 2-Wire Installation
- 120 V- 60 Hz Amp. Max. 1.25
- Master Carton: 32
- Inner Pack: 4



## 77875 WALL CONTROL

- For Fan with Light
- 3 Speeds (High/Medium/Low)
- Speed Control Fan and Light Brightness
- Wall Standard Installation
- Universal Receiver for Most Fan
- 120 V- 60 Hz Amp. Max. 1.25  
300 W Max.
- Master Carton: 32
- Inner Pack: 4



## 77873 WALL CONTROL

- For Fan with Light
- 4 Speeds  
(High/Medium High/Medium Low/Low)
- Turn Any Fan of 3 Speeds Into a 4 Speeds Fan
- Replace the Switch
- 120 V- 60 Hz Amp. Max. 1.25  
300 W Max.
- Master Carton: 32
- Inner Pack: 4



## 77870 REMOTE CONTROL

- For Fan with Light
- 3 Speeds (High/Medium/Low)
- Full Light with a Twist
- Operates at a Distance from 50 Feet
- Uses One Battery 9 volt (included)
- 120 V- 60 Hz Amp. Max. 1.25  
300 W Max.
- Master Carton: 32
- Inner Pack: 4



## 77105 CLEANER

- Electrostatic
- Extends up to 72" / 183cm
- Master Carton: 5



**77302**  
SET OF LIGHTING  
FIXTURES

- Antique Brass Finish
- White Schoolhouse Glass
- (1) Light Bulb 60W Max  
Standard Base (Not Included)
- Diameter: 9" / 22cm
- Master Carton: 4



**77304**  
SET OF LIGHTING  
FIXTURES

- White Finish
- White Schoolhouse Glass
- (1) Light Bulb 60W Max  
Standard Base (Not Included)
- Diameter: 9" / 22cm
- Master Carton: 4



**77305**  
SET OF LIGHTING  
FIXTURES

- White Finish
- White Globe Glass
- (1) Light Bulb 60W Max  
Standard Base (Not Included)
- Diameter: 8" / 20cm
- Master Carton: 4



**77203**  
SET OF LIGHTING  
FIXTURES  
INDOOR/OUTDOOR

- White Finish
- White Schoolhouse Glass
- (1) Light Bulb 60W Max  
Standard Base (Not Included)
- Diameter: 9" / 22cm
- Master Carton: 4



BASIC LIGHTING KITS



**77157**

- Antique Brass Finish
- (1) Light Bulb 60W Max  
Standard Base (Not Included)
- Lamp Up to: 4" / 10cm
- Master Carton: 12



**77155**

- White Finish
- (1) Light Bulb 60W Max  
Standard Base (Not Included)
- Lamp Up to: 4" / 10cm
- Master Carton: 12



**77152**

- Antique Brass Finish
- (1) Light Bulb 60W Max  
Standard Base (Not Included)
- Lamp Up to: 3 1/4" / 10cm
- Master Carton: 12



**77150**

- White Finish
- (1) Light Bulb 60W Max  
Standard Base (Not Included)
- Lamp Up to: 3 1/4" / 10cm
- Caja Maestra: 12

CATHEDRAL CANOPY KITS



**77060**

- Antique Brass Finish
- Canopy Bal Included to Down Rods of 1/2" / 1.27cm up to a 45° Angle
- Master Carton: 6



**77268**

- White Finish
- Canopy Bal Included to Down Rods of 1/2" / 1.27cm up to a 45° Angle
- Master Carton: 6

CATHEDRAL CANOPY BRACKETS



**77059**

- Black Finish
- Mounting Hardware Included
- Master Carton: 72
- Inner Pack: 6

REVERSIBLE BLADES REPLACEMENT



**77415**

- 5 Pieces
- 52" / 132cm
- Walnut & Oak Finish
- Master Carton: 24
- Inner Pack: 3



**77416**

- 5 Pieces
- 52" / 132cm
- White & Washed Oak Finish
- Master Carton: 24
- Inner Pack: 3

REVERSIBLE BLADES REPLACEMENT



**77410**

- 5 Pieces
- 42" / 106cm
- Walnut & Oak Finish
- Master Carton: 24
- Inner Pack: 3



**77411**

- 5 Pieces
- 42" / 106cm
- White & Washed Oak Finish
- Master Carton: 24
- Inner Pack: 3

FAN BLADE ARMS REPLACEMENT



**77407**

- 5 Pieces
- 52" / 132cm
- Antique Brass Finish
- Master Carton: 24
- Inner Pack: 6



**77406**

- 5 Pieces
- 52" / 132cm
- White Finish
- Master Carton: 24
- Inner Pack: 6



**77402**

- 5 Pieces
- 42" / 106cm
- Antique Brass Finish
- Master Carton: 24
- Inner Pack: 3



**77401**

- 5 Pieces
- 42" / 106cm
- White Finish
- Master Carton: 24
- Inner Pack: 3

SWITCHES WITH PULL CHAIN



**77021**

- 3 Speeds
- 4 Wire Unit
- Master Carton: 72
- Inner Pack: 6



**77075**

- 3 Speeds
- 8 Wire Unit
- Master Carton: 72
- Inner Pack: 6

LIGHTING SWITCHES



**77023**


- Light Switch with Pull Chain
- Master Carton: 72
- Inner Pack: 6



**77052**

- 3-Way Light Switch with Pull Chain
- Master Carton: 72
- Inner Pack: 6

FAN CAPACITORS



**77090**

- 3 Wire
- 1.5 MFD y 3 MFD
- Master Carton: 72
- Inner Pack: 6


**77091**

- 3 Wire
- 3 MFD y 6.5 MFD
- Master Carton: 72
- Inner Pack: 6

**77092**

- 3 Wire
- 6 MFD y 14 MFD
- Master Carton: 72
- Inner Pack: 6


CHAIN CONNECTORS



**77049**


- Stainless Steel Finish
- 3 Feet
- Master Carton: 72
- Inner Pack: 6

CHAIN CONNECTORS




**77064**

- Antique Bras Finish
- 3 Feet
- Master Carton: 72
- Inner Pack: 6




**77050**

- Polished Brass Finish
- 3 Feet
- Master Carton: 72
- Inner Pack: 6



**77051**

- White Finish in Plastic
- 3 Feet
- Master Carton: 72
- Inner Pack: 6



**77238**

- Brushed Pewter Finish
- 3 Feet
- Master Carton: 72
- Inner Pack: 6

PULL CHAINS

**77225**

- Blade Design
- White Finish
- Master Carton: 72
- Inner Pack: 6



**77224**

- Blade Design
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77007**

- Sculptured Wooden Ball  
Walnut Finish
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77095**

- Gold Metal and Ceramic
- Acabado Dorado
- Master Carton: 72
- Inner Pack: 6



**77550**

- Transparent Acrylic  
with Drop Design
- Polished Pewter Finish
- Master Carton: 72
- Inner Pack: 6



**77639**

- Glass with Yellow  
Spiral Design
- Nickel Finish
- Master Carton: 72
- Inner Pack: 6



**77087**

- Wooden Design
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**70661**

- Sphere-Shaped Design  
in Walnut Wooden
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77013**

- Wooden Knob Shaped  
Design Walnut Finish
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77014**

- Wooden Knob Shaped  
Design White Finish
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77620**

- Sphere Shaped Design  
with Colored Dots
- Nickel Finish
- Master Carton: 72
- Inner Pack: 6



**77621**

- Sphere Shaped Design  
with Blue Swirls
- Nickel Finish
- Master Carton: 72
- Inner Pack: 6





PULL CHAINS

**77088**

- Drop Design in Transparent Acrylic
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77006**

- Cylinder Design in Transparent Acrylic
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77134**

- Dolphin Design in Transparent Acrylic
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77084**

- Design in Clear Acrylic Ball
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77635**

- Filigree Leaf in Transparent Glass
- Polished Pewter Finish
- Master Carton: 72
- Inner Pack: 6



**77039**

- Trophy Shaped Design
- White Finish
- Master Carton: 72
- Inner Pack: 6



**77215**

- Trophy Shaped Design
- Brushed Pewter Color
- Master Carton: 72
- Inner Pack: 6



**77108**

- Trophy Shaped Design
- Antique Brass Finish
- Master Carton: 72
- Inner Pack: 6



**77130**

- Baseball Bat
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77128**

- Futball Soccer Ball
- Bronze Finish
- Master Carton: 72
- Inner Pack: 6



**77019**

- Cone-Shaped Design in Natural Wooden
- Golden Finish
- Master Carton: 72
- Inner Pack: 6




**77008**

- Cone-Shaped Design in Walnut Wooden
- Golden Finish
- Master Carton: 72
- Inner Pack: 6




# DOWN RODS



**FINISHES**

			
Antique Brass	Brushed Pewter	Polished Brass	Satin Brass
			
Rustic Bronze	Iron	Oil Rubbed Bronze	Old Chicago
			
White	Brushed Nickel		



## Down Rod 1/2" I.D.

Finished	12"	18"	24"	36"	Master Carton	Inner Pack
Antique Brass	77241	77263	77244	77247	24	6
Brushed Pewter	---	77485	77486	77487	6	---
Polished Brass	77242	---	77245	77248	24	6
White	77240	77262	77243	77246	24	6

## Down Rod 3/4" I.D.

Finished	12"	24"	Master Carton	Inner Pack
Antique Brass	77249	77252	24	6
Brushed Nickel	77526	77527	6	---
Brushed Pewter	77509	77510	6	---
Old Chicago	77515	77516	6	---
Satin Brass	77582	---	6	---
Polished Brass	---	77253	24	6
White	77251	77254	24	6
Rustic Bronze	65659	65661	24	6
Iron	65606	65608	24	6
Oil Rubbed Bronze	---	65682	24	6



# PORTABLE FANS

Products Available in 120 V- / 220 V-, 50 Hz / 60 Hz








### Easy Install

Ready to install in three easy steps.




### Efficiency Engine

Equipped with a powerful and high efficiency engine.



### Low Level of Noise

Cutting edge design and high technology in his parts.



### Fuse

This product employs overload protection (fuse). A blown fuse indicates an overload or short circuit situation.





**72708**  
TOWER FAN  
76 cm / 30"

- White Finish
- Blades & Grill in ABS Plastic
- Time Control
- Manual Control
- Oscillating Function
- 3 Speed



**72710**  
TOWER FAN  
93 cm / 37"

- Black Finish
- Blades & Grill in ABS Plastic
- Time Control
- Infrared Remote Control
- Oscillating Function
- 3 Speed



Included



**72709**  
TOWER FAN  
93 cm / 32"

- Gray Finish
- Blades & Grill in ABS Plastic
- Time Control
- Infrared Remote Control
- Oscillating Function
- 3 Speed



Included







**72713**  
FLOOR FAN  
40 cm / 16"



- Dark Grey & Black Finish
- Plastic Blades & Grill
- Adjustable Angle
- Manual Control
- 3 Speed

**72706**  
FLOOR FAN  
40 cm / 16"



Included

- Dark Grey & Black Finish
- Plastic Blades & Grill
- Adjustable Angle
- Remote Control
- 3 Speed

**72705**  
FLOOR FAN  
50 cm / 20"



- Dark Grey & Black Finish
- Plastic Blades & Grill
- Adjustable Angle
- Manual Control
- 3 Speed





**72716**  
INDUSTRIAL  
FLOOR FAN  
50 cm / 20"



- Black & Silver Finish
- Metal Blades ABS & Grill
- Adjustable Angle
- Manual Control
- 3 Speed

**72715**  
INDUSTRIAL  
STAND FAN  
40 cm / 20"



- Black & Silver Finish
- Metal Blades ABS & Grill
- Oscillating Function
- Manual Control
- 3 Speed

**72717**  
INDUSTRIAL  
FLOOR FAN  
35 cm / 14"



- Black & Silver Finish
- Metal Blades ABS & Grill
- Adjustable Angle
- Oscillating Function
- Manual Control
- 3 Speed

IDEAL FOR COMMERCIAL  
APPLICATIONS





**72700**  
STAND FAN  
40 cm / 16"

- White Finish
- Plastic Blades & Grill
- Oscillating Function
- Manual Control
- 3 Speed



**72701**  
STAND FAN  
40 cm / 16"

- Black Finish
- Plastic Blades & Grill
- Oscillating Function
- Manual Control
- 3 Speed





**72702**  
STAND FAN  
40 cm / 16"

- White Finish
- Plastic Blades & Grid
- Oscillating Function
- Remote Control
- Time Control
- Silent Mode
- 3 Speed



Included




**72703**  
STAND FAN  
40 cm / 16"

- Black Finish
- Plastic Blades & Grid
- Oscillating Function
- Remote Control
- Time Control
- Silent Mode
- 3 Speed



Included







**72704**  
WALL FAN  
40 cm / 16"



Included



- White Finish
- Plastic Blades & Grill
- Oscillating Function
- Remote Control
- Control de Tiempo
- 3 Speed

**72707**  
WALL FAN  
40 cm / 16"



- White Finish
- Plastic Blades & Grill
- Oscillating Function
- Control Manual
- 3 Speed

**72712**  
DESK FAN  
40 cm / 16"



- White Finish
- Plastic Blades & Metal Grill
- Oscillating Function
- Rotary Control
- 3 Speed







**72714**  
TABLE, WALL, STAND  
40 cm / 16"

- White Finish
- Blades & Plastic Grill
- Oscillating Function
- Manual Control
- 3 Speed





LIGHTING FIXTURES  
COLLECTION

...



## INDOOR CEILING LIGHTING FIXTURES

...



64304



64305



64306



66378



64300



64301

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
64300	White	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	10
64301	White	Frosted Opal with Spiral Design	(3) 60 W Max. Base Std. (Not Included)	6 1/2" - 16.5 cm	15" - 38 cm	6
64304	Brushed Nickel	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (No include)	5 7/8" - 14.9 cm	11" - 27.9 cm	6
64305	Brushed Nickel	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	10
64306	Brushed Nickel	Frosted Opal with Spiral Design	(3) 60 W Max. Base Std. (Not Included)	6 1/2" - 16.5 cm	15" - 38 cm	6
66378	Brushed Nickel	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	6





64290



64291



64292



64307



64308



64309

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
64290	Oil Rubbed Bronze	Frosted Alabaster Opal	(1) 60 W Max. Base Std. (Not Included)	6 1/2" - 14 cm	11" - 27.9 cm	6
64291	Oil Rubbed Bronze	Frosted Alabaster Opal	(2) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	13" - 33 cm	10
64292	Oil Rubbed Bronze	Frosted Alabaster Opal	(3) 60 W Max. Base Std. (Not Included)	5 5/8" - 16.8 cm	15" - 38.91 cm	6
64307	Sienna	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	6
64308	Sienna	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/2" - 16.5 cm	15" - 38 cm	6
66309	Sienna	Frosted Opal with Spiral Design	(3) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	10





64325



66327



66069



66055



64302



66095



66162



66161



67142

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
64302	Polished Brass	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	10
64325	Antique Brass	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	6" - 15.2 cm	11" - 27.9 cm	6
66055	Antique Brass	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	6
66069	Iron	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	6
66095	Iron	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	12
66161	White	Frosted & Clear Opal with Floral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/4" - 15.8 cm	11 1/4" - 28.5 cm	6
66162	White	Frosted & Clear Opal with Floral Design	(2) 60 W Max. Base Std. (Not Included)	7" - 17.7 cm	13 1/4" - 33.6 cm	10
66327	Polished Brass	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 9.2 cm	11" - 27.9 cm	6
67142	Sienna	Frosted Dome with Ribbed Design	(2) 60 W Max. Base Std. (Not Included)	7 1/2" - 19 cm	13 1/2" - 34.2 cm	6



38124



38126



38125



38120



38123



38121



38122



Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
38120	Sienna	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	4 (2 Pieces)
38121	Brushed Nickel	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	4 (2 Pieces)
38122	Antique Brass	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	4 (2 Pieces)
38123	White	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	4 (2 Pieces)
38124	Brushed Nickel	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	2 (2 Pieces)
38125	Antique Brass	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	2 (2 Pieces)
38126	White	Frosted Opal with Spiral Design	(2) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	13" - 33 cm	2 (2 Pieces)



67334



67347



67378



67875

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
67334	Brushed Nickel	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	3 (2 Pieces)
67378	White	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	3 (2 Pieces)
67875	Antique Brass	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	3 (2 Pieces)
67347	Sienna	Frosted Opal with Spiral Design	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 14.9 cm	11" - 27.9 cm	3 (2 Pieces)



66203



67209



66681



66699



66698



66604



66611



66610

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
66203	White	Clear with Dither Design	(2) 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	8 3/4" - 21 cm	12
66604	Antique Brass	Clear Opal with Floral Design	(1) 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	7 1/2" - 19 cm	12
66610	Antique Brass	Clear Opal with Dither Design	(2) 60 W Max. Base Std. (Not Included)	5 1/2" - 14 cm	9 1/2" - 24.1 cm	6
66611	White	White Opal	(2) 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	9 1/2" - 24.1 cm	6
66681	Antique Brass	White Opal	(1) 60 W Max. Base Std. (Not Included)	4 3/4" - 12 cm	7 1/2" - 19 cm	12
66698	Polished Brass	Clear Opal with Dither Design	(1) 60 W Max. Base Std. (Not Included)	5 1/2" - 14 cm	9 1/2" - 24.1 cm	6
66699	White	White Opal	(1) 60 W Max. Base Std. (Not Included)	4 3/4" - 12 cm	7 3/4" - 19.6 cm	12
67209	Brushed Nickel	Frosted Dome with Line Design	(1) 60 W Max. Base Std. (Not Included)	4" - 10.1 cm	6 7/8" - 17.4 cm	12



64629



64631



64671



66329



64669



67358



66206

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
64629	Pewter	White Opal	(1) 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	11 3/4" - 28.9 cm	6
64631	White	White Opal	(1) 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	11 3/4" - 28.9 cm	6
64669	Antique Pewter	Frosted Opal with Line Design	(1) 60 W Max. Base Std. (Not Included)	4 5/8" - 11.7cm	7 1/2" - 19 cm	6
64671	White	Frosted Opal with Line Design	(1) 60 W Max. Base Std. (Not Included)	4 5/8" - 11.7cm	7 1/2" - 19 cm	6
66206	White	White Opal with Clear Design	(3) 60 W Max. Base Std. (Not Included)	6 1/4" - 15.8 cm	13" - 33 cm	12
66329	Polished Brass	Frosted Opal with Line Design	(1) 60 W Max. Base Std. (Not Included)	4 5/8" - 11.7cm	7 1/2" - 19 cm	6
67358	Brushed Nickel	Frosted Opal	(1) 60 W Max. Base Std. (Not Included)	3 1/8" - 8 cm	11 3/4" - 28.9 cm	6





66201



67211



66263



66600



66607



66677



66692



66679

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
66201	White	White Square with Clear Edge	(3) 60 W Max. Base Std. (Not Included)	6" - 15.8 cm	14 1/2" - 36.8 cm	12
66211	White	White Square with Line Design	(2) 60 W Max. Base Std. (Not Included)	6 1/4" - 15.8 cm	13 3/4" - 39 cm	12
66263	White	White Square with Floral & Leaf Design	(2) 60 W Max. Base Std. (Not Included)	6 1/4" - 15.8 cm	11 1/2" - 29.2 cm	12
66600	Antique Brass	White Globe	(1) 60 W Max. Base Std. (Not Included)	7 1/4" - 18.4 cm	6" - 15 cm	12
66607	White	White Globe	(1) 60 W Max. Base Std. (Not Included)	7 1/4" - 18.4 cm	6" - 15 cm	12
66677	Polished Brass	White Globe	(1) 60 W Max. Base Std. (Not Included)	7 1/4" - 18.4 cm	6" - 15 cm	12
66679	Antique Brass	Clear Acorn	(1) 60 W Max. Base Std. (Not Included)	7 1/4" - 18.4 cm	5 1/4" - 13.3 cm	12
66692	Polished Brass	Clear Globe	(1) 60 W Max. Base Std. (Not Included)	7 1/4" - 18.4 cm	6" - 15 cm	12



SET OF LIGHTING FIXTURES

...



67418



67419



67364



67357



67353



67352



67356



67363

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter/Width	Master Carton
67352	Detalles en Blanco	Frosted Opal	(1) 60 W Max. Base Std. (Not Included)	5 7/8" - 15 cm	11 3/4" - 29.8 cm	6
67353	Detalles en Blanco	Frosted Opal	(1) 60 W Max. Base Std. (Not Included)	3 1/2" - 8.8 cm	11 3/4" - 28.9 cm	6
67356	Antique Copper Details	White Marbleized Murano Glass	(1) 60 W Max. Base Std. (Not Included)	3 7/8" - 9.8 cm	11 3/4" - 28.9 cm	6
67357	Antique Copper Details	Amber Marbleized Murano Glass	(1) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	11 3/4" - 29.8 cm	6
67363	Antique Copper Details	White Marbleized Murano Glass	(1) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	11 3/4" - 29.8 cm	6
67364	Antique Copper Details	Amber Marbleized Murano Glass	(1) 60 W Max. Base Std. (Not Included)	4 1/8" - 10.4 cm	11 3/4" - 28.9 cm	6
67418	Antique Copper Details	Gray Marbleized Murano Glass	(1) 60 W Max. Base Std. (Not Included)	3 1/8" - 8 cm	11 3/4" - 28.9 cm	6
67419	Antique Copper Details	Gray Marbleized Murano Glass	(1) 60 W Max. Base Std. (Not Included)	6 1/8" - 15.5 cm	11 3/4" - 29.8 cm	6



Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter/Width	Master Carton
67354	Chrome Details	Opalino Esmerilado	(1) 60 W Max. Base Std. (Not Included)	3 5/8" - 9.2 cm	11 5/8" - 29.5 cm	6
67355	Chrome Details	Opalino Esmerilado	(1) 60 W Max. Base Std. (Not Included)	9 3/4" - 24.7 cm	8" - 20.3 cm	6
66373	White	Frosted Ruffled Edge Glass	(1) 60 W Max. Base Std. (Not Included)	5" - 15.2 cm	5 3/4" - 14.6 cm	12
66374	White	Frosted Ruffled Edge Glass	(3) 60 W Max. Base Std. (Not Included)	6 1/4" - 15.8 cm	13 1/8" - 33.3 cm	4
66376	White	Frosted Ruffled Edge Glass	(2) 100 W Max. Base Std. (Not Included)	8 1/4" - 21 cm	9 1/2" - 27.9 cm	6
66375	White	Frosted Ruffled Edge Glass	(1) 60 W Max. Base Std. (Not Included)	7 1/2" - 19 cm	5 3/4" - 14.6 cm	6





## INDOOR WALL LIGHTING FIXTURES

...





66494



66685



64617



67199



66683



66496

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
66494	Antique Pewter with On/Off Switch	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	9 3/4" - 24.7 cm	5 1/4" - 13.3 cm	6
64617	Brushed Nickel	White Glass	(2) 60 W Max. Base Std. (Not Included)	8 1/2" - 21.5 cm	13 1/2" - 34.2 cm	4
66496	Brushed Nickel	White Glass	(1) 60 W Max. Base Std. (Not Included)	7" - 17.7 cm	5 1/4" - 13.3 cm	6
66683	Antique Brass	Frosted Glass	(1) 100 W Max. Base Std. (Not Included)	8" - 20.3 cm	5 7/8" - 15 cm	6
66685	Antique Brass	Frosted Glass	(2) 60 W Max. Base Std. (Not Included)	8 1/4" - 8 cm	11 1/2" - 29.8 cm	6
67199	Antique Brass	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	8 3/4" - 22.2 cm	5" - 12.7 cm	6



# INDOOR WALL LIGHTING FIXTURES



66654



66601



67179



66403



66401



66402



66594



66448



66406

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
66401	White	White	(1) 75 W Max. Base Std. (Not Included)	7 1/2" - 15.2 cm	4 1/2" - 11.4 cm	12
66402	Chrome, with ON / OFF Chain	White	(1) 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	5 1/4" - 13.3 cm	12
66403	White	White	(1) 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	14" - 35.5 cm	6
66406	Chrome	---	(3) G25 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	18" - 45.7 cm	6
66448	Beveled Mirror	---	(3) G25 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	18" - 45.7 cm	6
66594	White	---	(3) G25 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	18" - 45.7 cm	6
66601	Polished Brass with ON / OFF Switch	Frosted Glass with Design	(1) 60 W Max. Base Std. (Not Included)	8" - 20.3 cm	4 1/2" - 11.4 cm	12
66654	Brushed Nickel with ON / OFF Switch	Frosted Glass with Design	(1) 60 W Max. Base Std. (Not Included)	8" - 20.3 cm	4 1/2" - 11.4 cm	12
67179	Antique Brass with ON / OFF Switch	Frosted Glass with Design	(1) 60 W Max. Base Std. (Not Included)	8" - 20.3 cm	4 1/2" - 11.4 cm	12



64022



64025



64023



64024

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
64022	Matted Chrome	Frosted	(1) 60 W Max. Base Std. (Not Included)	7 1/8" - 18 cm	11" - 28 cm	8
64023	Matted Chrome	Frosted	(1) 60 W Max. Base Std. (Not Included)	7 1/8" - 18 cm	11" - 28 cm	8
64024	Matted Chrome	Frosted	(1) 60 W Max. Base Std. (Not Included)	7 1/8" - 18 cm	11" - 28 cm	8
64025	Matted Chrome	Frosted	(1) 60 W Max. Base Std. (Not Included)	7 1/8" - 18 cm	11" - 28 cm	8



LIGHTING FIXTURES PENDANTS

...





64014



64016



64015

Item	Lighting Fixture	Glass Type	Bulb	Max Height	Diameter	Master Carton
64014	Chrome Finish	Cone Type with Details	(1) 60 W Max. Base Std. (Not Included)	50" - 127 cm	3 1/4" - 8.3 cm	12
64015	Chrome Finish	Cylinder Type with Details	(1) 60 W Max. Base Std. (Not Included)	50" - 127 cm	3 1/5" - 8.9 cm	12
64016	Chrome Finish	Bell Type with Details	(1) 60 W Max. Base Std. (Not Included)	50" - 127 cm	4 1/8" - 10.4 cm	12





CEILING  
REFLECTORS

...



64033



64035



64037



64032



64034



64036

Item	Ceiling Reflectors	Bulb	Height	Diameter	Master Carton
64032	White	(1) R20 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	5 3/4" - 14.6 cm	12
64033	Matted Chrome	(1) R20 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	5 3/4" - 14.6 cm	12
64034	White	(2) R20 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	6 7/8" - 17.4 cm	12
64035	Matted Chrome	(2) R20 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	6 7/8" - 17.4 cm	12
64036	White	(3) R20 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	13 3/4" - 35 cm	8
64037	Matted Chrome	(3) R20 60 W Max. Base Std. (Not Included)	5" - 12.7 cm	13 3/4" - 35 cm	8



FIXED DOWN LIGHTS





66127



66125



66124



66126



66123



66129



66130



66132

Item	Fixed Down Light	Glass Type	Bulb	Height	Diameter	Master Carton
66123	White	---	(2) 26 W Max. Base Std. (Not Included)	5 5/16" - 13.4 cm	9 1/8" - 23.1 cm	10
66124	White	---	(2) 19 W Max. Base Std. (Not Included)	4 1/8" - 10.4 cm	7 1/2" - 19 cm	10
66125	White	Frosted	(2) 18 W Max. Base Std. (Not Included)	4 1/8" - 10.4 cm	7 1/2" - 19 cm	10
66126	White	Clear Hatched	(2) 18 W Max. Base Std. (Not Included)	3 15/16" - 10 cm	8 7/8" - 22.5 cm	10
66127	White	Clear Hatched	(2) 18 W Max. Base Std. (Not Included)	3 3/4" - 9.5 cm	6 1/4" - 15.8 cm	10
66129	White	Frosted	(2) 26 W Max. Base Std. (Not Included)	3 7/16" - 8.7 cm	9 1/16" - 23 cm	10
66130	Brushed Nickel	Semi-Clear	(2) 9 W Max. Base Std. (Not Included)	2 7/16" - 6.1 cm	10 5/8" - 27 cm	10
66132	White	Clear Hatched	(2) 26 W Max. Base Std. (Not Included)	3 15/16" - 10 cm	9 1/16" - 23 cm	10





66120



66122



66119



64139



64140



Item	Fixed Down Light	Bulb	Height	Diameter	Master Carton
66119	Fixed Down Light, White (adjustable)	(1) 18 W Max. Base Std. (Not Included)	4 1/8" a 5 1/8" 10.4 cm a 13.3 cm	4 3/4" - 12 cm	20
66120	Fixed Down Light, White (adjustable)	(1) 18 W Max. Base Std. (Not Included)	5 13/16" a 8 1/8" 14.7 cm a 20.6 cm	5 3/4" - 14.6 cm	20
66122	Fixed Down Light, White (adjustable)	(1) 18 W Max. Base Std. (Not Included)	7 1/16" a 9 5/16" 18 cm a 23.6 cm	6 7/8" - 17.4 cm	20

Item	Fixed Down Light	Bulb	Master Carton
64139	Fixed Halogen Down Light, White	(1) 50 W Max. Base GU10 (Included)	(3 Pieces) 12
64140	Fixed Halogen Down Light, Brushed Nickel	(1) 50 W Max. Base GU10 (Included)	(3 Pieces) 12

120V Direct  
without Transformer





64131




64130




64132



64142



64149



64144



64143



64141

Item	Fixed Down Light	Bulb	Master Carton
64130	Fixed Halogen Down Light, White	(1) 50 W Max. Base GU10 (Included)	24
64131	Fixed Halogen Down Light, Brushed Nickel	(1) 50 W Max. Base GU10 (Included)	24
64132	Fixed Halogen Down Light, Chrome	(1) 50 W Max. Base GU10 (Included)	24
64141	Swivel Halogen Down Light, White	(1) 50 W Max. Base GU10 (Included)	24
64142	Swivel Halogen Down Light, Brushed Nickel	(1) 50 W Max. Base GU10 (Included)	24
64143	Fixed Halogen Down Light, Chrome	(1) 50 W Max. Base GU10 (Included)	24
64144	Swivel Halogen Down Light, Antique Brass	(1) 50 W Max. Base GU10 (Included)	24
64149	Fixed Halogen Down Light, Copper	(1) 50 W Max. Base GU10 (Included)	24

120V Direct  
without Transformer



## DESK LIGHTING FIXTURES





64448



64449



64482



64452



64453

With Switch  
On / Off



64483

Item	Desk Lighting Fixture	Bulb	Height	Width	Cord	Master Carton
64448	Black & White, Adjustable	(1) 60 W Max. Base Std. (Not Included)	10 1/2" - 26.6 cm	4 1/4" - 10.7 cm	72" - 192 cm	12
64449	Black, Adjustable	(1) 60 W Max. Base Std. (Not Included)	10 1/2" - 26.6 cm	4 1/4" - 10.7 cm	72" - 192 cm	12
64452	Black & White, Adjustable	(1) 60 W Max. Base Std. (Not Included)	18" - 45.7 cm	5 1/2" - 14 cm	72" - 192 cm	12
64453	Black, Adjustable	(1) 60 W Max. Base Std. (Not Included)	18" - 45.7 cm	5 1/2" - 14 cm	72" - 192 cm	12
64482	Black & Gray, Adjustable	(1) 60 W Max. Base Std. (Not Included)	10 1/2" - 26.6 cm	4 1/4" - 10.7 cm	72" - 192 cm	12
64483	Black & Gray, Adjustable	(1) 60 W Max. Base Std. (Not Included)	18" - 45.7 cm	5 1/2" - 14 cm	72" - 192 cm	12



# OUTDOOR CEILING LIGHTING FIXTURES

...





66840



66975



66976



66919



66822



66823

Item	Lighting Fixture	Glass Type	Bulb	Height	Diameter	Master Carton
66822	Black Resin	Clear Acrylic Textured Panels	(1) 60 W Max. Base Std. (Not Included)	4 3/4" - 12 cm	8 1/4" - 24.1 cm	6
66823	Black Resin	Clear Acrylic Textured Panels	(2) 60 W Max. Base Std. (Not Included)	5 1/2" - 14 cm	10 1/4" - 26 cm	6
66840	Black Resin	White Glass Globe	(1) 60 W Max. Base Std. (Not Included)	7 1/4" - 18.4 cm	6" - 15 cm	6
66919	Black	Clear Cilindric Glass	(1) 60 W Max. Base Std. (Not Included)	6" - 15.2 cm	4 3/4" - 12 cm	12
66975	White Resin	Clear Acrylic Textured Panels	(1) 60 W Max. Base Std. (Not Included)	4 3/4" - 12 cm	8 1/4" - 24.1 cm	6
66976	White Resin	Clear Acrylic Textured Panels	(2) 60 W Max. Base Std. (Not Included)	5 1/2" - 14 cm	10 1/4" - 26 cm	6





OUTDOOR WALL  
LIGHTING FIXTURES

...



67863



67864



64683



66826



66828



64691

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
64683	Antique Brass	Clear Beveled Glass Panels	(1) 100 W Max. Base Std. (Not Included)	19 1/4" - 48.8cm	6 5/8" - 16.8 cm	6
64691	Antique Brass	Frosted	(1) 100 W Max. Base Std. (Not Included)	15" - 38.1 cm	6 1/2" - 16.5 cm	6
66826	Textured Black	Frosted	(1) 100 W Max. Base Std. (Not Included)	15" - 38.1 cm	6 1/2" - 16.5 cm	6
66828	Textured White	Frosted	(1) 100 W Max. Base Std. (Not Included)	15" - 38.1 cm	6 1/2" - 16.5 cm	6
67863	Black	Clear Beveled Glass Panels	(1) 100 W Max. Base Std. (Not Included)	19 1/4" - 48.8cm	6 5/8" - 16.8 cm	6
67864	White	Clear Beveled Glass Panels	(1) 100 W Max. Base Std. (Not Included)	19 1/4" - 48.8cm	6 5/8" - 16.8 cm	6



# OUTDOOR WALL LIGHTING FIXTURES



66097



66839



66974



66878



66885



66800

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
66097	Brushed Nickel	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	7 1/2" - 19 cm	4 1/2" - 11.4 cm	12
66800	Resin Black	Clear Glass	(1) 60 W Max. Base Std. (Not Included)	6" - 15.2 cm	4 1/4" - 10.7 cm	12
66839	Antique Brass	Clear Glass	(1) 60 W Max. Base Std. (Not Included)	7 1/2" - 19 cm	4 1/2" - 11.4 cm	12
66878	White	Clear Glass	(1) 60 W Max. Base Std. (Not Included)	7 1/2" - 19 cm	4 1/2" - 11.4 cm	12
66885	Black	Clear Glass	(1) 60 W Max. Base Std. (Not Included)	7 1/2" - 19 cm	4 1/2" - 11.4 cm	12
66974	Resin White	Clear Glass	(1) 60 W Max. Base Std. (Not Included)	6" - 15.2 cm	4 1/4" - 10.7 cm	12





66983



66984



64687



66946



66860



66859

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
66946	Resin White	Clear Textured Acrylic Panels	(1) 60 W Max. Base Std. (Not Included)	17" - 43.1cm	8" - 20.3 cm	6
66859	Resin Black	Clear Textured Acrylic Panels	(1) 60 W Max. Base Std. (Not Included)	8" - 20.3 cm	7 1/4" - 18.4 cm	6
66860	Resin Black	Clear Textured Acrylic Panels	(1) 60 W Max. Base Std. (Not Included)	17" - 43.1cm	8" - 20.3 cm	6
66983	Black	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	13 1/2" - 34.2 cm	10 1/4" - 26 cm	6
66984	White	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	13 1/2" - 34.2 cm	10 1/4" - 26 cm	6
64687	Textured Rust Patina	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	13 1/2" - 34.2 cm	10 1/4" - 26 cm	6



# OUTDOOR WALL LIGHTING FIXTURES



66962



66898



66971



66961



67889



66972

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
66961	Black	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	7 3/4" - 15.8 cm	6" - 15.2 cm	12
66962	White	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	7 3/4" - 15.8 cm	6" - 15.2 cm	12
66971	Textured White	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	8 1/4" - 24.1 cm	4 1/2" - 11.4 cm	12
66972	Textured Black	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	8 1/4" - 24.1 cm	4 1/2" - 11.4 cm	12
67889	Black	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	9 7/8" - 25 cm	7 7/8" - 20 cm	6
66898	White	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	9 7/8" - 25 cm	7 7/8" - 20 cm	6





67835



64151



64150



67836



64153



64152

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
64150	Black	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	4 1/4" - 10.7 cm	8 1/2" - 21.5 cm	12
64151	Brushed Nickel	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	4 1/4" - 10.7 cm	8 1/2" - 21.5 cm	12
64152	Black	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	8" - 20.3 cm	12
64153	Brushed Nickel	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	8" - 20.3 cm	12
67835	White	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	4 1/4" - 10.7 cm	8 1/2" - 21.5 cm	12
67836	White	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	4 1/2" - 11.4 cm	8" - 20.3 cm	12



# OUTDOOR WALL LIGHTING FIXTURES



66945



66803



66166



67972



66879



66881



67831



67834

Item	Lighting Fixture	Glass Type	Bulb	Height	Width	Master Carton
66166	White	Frosted Glass	(1) 100 W Max. Base Std. (Not Included)	6 1/2" - 16.5 cm	4 1/4" - 10.7 cm	8
66803	Black	White Glass Globe	(1) 60 W Max. Base Std. (Not Included)	7 1/4" - 18.4 cm	6" - 15.2 cm	6
66879	Textured White	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	8 1/2" - 21.5 cm	6" - 15.2 cm	6
66881	Textured Black	Frosted Glass	(1) 60 W Max. Base Std. (Not Included)	8 1/2" - 21.5 cm	6" - 15.2 cm	6
66945	White	White Glass Globe	(1) 60 W Max. Base Std. (Not Included)	7 1/4" - 18.4 cm	6" - 15.2 cm	6
67831	Textured Black	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	12" - 30.4cm	6 1/2" - 16.5 cm	6
67834	Textured White	Clear Glass Panels	(1) 100 W Max. Base Std. (Not Included)	12" - 30.4cm	6 1/2" - 16.5 cm	6
67972	Textured Black	Frosted Glass	(1) 100 W Max. Base Std. (Not Included)	6 1/2" - 16.5 cm	4 1/4" - 10.7 cm	8



LIGHTING FIXTURES  
ACCESSORIES

...

## CANOPY KITS

### 70056

- Hole in the Center
- White Finish
- 1 Crossbar
- 1 Screw Collar Loop
- 4 Mounting Screws
- 1 Locknut
- 2 Cap Nut
- Diameter: 5"/12.7cm
- Center Hole: 7/16" / 1.1cm
- Master Carton: 48
- Inner Pack: 4



### 70052

- Hole in the Center
- Bronze Finish
- 1 Crossbar
- 1 Screw Collar Loop
- 4 Mounting Screws
- 1 Locknut
- 2 Cap Nut
- Diameter: 5" / 12.7cm
- Center Hole: 7/16" / 1.1cm
- Master Carton: 48
- Inner Pack: 4



### 70053

- Hole in the Center
- Antique Brass Finish
- 1 Crossbar
- 1 Screw Collar Loop
- 4 Mounting Screws
- 1 Locknut
- 2 Cap Nut
- Diameter: 5"/12.7cm
- Center Hole: 7/16" / 1.1cm
- Master Carton: 48
- Inner Pack: 4



### 70038

- Hole in the Center
- Oil Rubbed Bronze Finish
- 1 Screw Collar Loop
- 2 Mounting Screw
- 1 Lock Washer
- 1 Locknut
- Diameter: 5" / 12.7cm
- Center Hole: 7/16"/1.1cm
- Master Carton: 48
- Inner Pack: 4



### 70059

- Hole in the Center
- Brushed Pewter
- 1 Screw Collar Loop
- 2 Mounting Screw
- 1 Lock Washer
- 1 Locknut
- Diameter: 5" / 12.7cm
- Center Hole: 7/16"/1.1cm
- Master Carton: 48
- Inner Pack: 4



### 70033

- Hole in the Center
- Brushed Nickel Finish
- 1 Screw Collar Loop
- 2 Mounting Screw
- 1 Lock Washer
- 1 Locknut
- Diameter: 5" / 12.7cm
- Center Hole: 7/16"/1.1cm
- Master Carton: 48
- Inner Pack: 4



## CANOPY KITS

### 70034

- Hole in the Center
- Bronze Finish
- 1 Screw Collar Loop
- 2 Mounting Screw
- 1 Lock Washer
- 1 Locknut
- Diameter: 5" / 12.7cm
- Center Hole: 7/16"/1.1cm
- Master Pack: 48
- Inner Pack: 4



### 70037

- Hole in the Center
- White Finish
- 1 Screw Collar Loop
- 2 Mounting Screw
- 1 Lock Washer
- 1 Locknut
- Diameter: 5" / 12.7cm
- Center Hole: 7/16"/1.1cm
- Master Pack: 48
- Inner Pack: 4



### 70035


- Hole in the Center
- Antique Brass Finish
- 1 Screw Collar Loop
- 2 Mounting Screw
- 1 Lock Washer
- 1 Locknut
- Diameter: 5" / 12.7cm
- Center Hole: 7/16"/1.1cm
- Master Pack: 48
- Inner Pack: 4



## CHAINS

### 70071

- Antique Brass Finish
- 3Ft. - Gauge 1
- Supports 35 lbs or Less
- Master Pack: 72
- Inner Pack: 6



### 70070

- Polished Brass Finish
- 3Ft. - Gauge 1
- Supports 35 lbs or Less
- Master Pack: 72
- Inner Pack: 6



## CHAINS

### 70670

- White Finish
- 3Ft. - Gauge 1
- Supports 35 lbs or Less
- Master Pack: 72
- Inner Pack: 6



### 70671

- Brushed Pewter Finish
- 3Ft. - Gauge 1
- Supports 35 lbs or Less
- Master Pack: 72
- Inner Pack: 6



## CROSSBARS

### 70113

- From 4"/10.2cm
- Tapped 1/8"/0.3cm-IP
- Master Pack: 144
- Inner Pack: 6



### 70114

- From 4"/10.2cm
- Green Ground Screw
- Master Pack: 144
- Inner Pack: 6





## NIPLES



### 70603

- 3"/7.6cm Length
- 2 Units
- Zinc Plated Finish
- Thread 1/8-IP/0.3cm
- Master Carton: 144
- Inner Pack: 6

## LAMP PIPES



### 70270

- From 30"/76.2cm
- Bronze Finish
- Thread 1/8-IP/0.3cm
- Master Carton: 72
- Inner Pack: 6

## REPLACEMENT KNOBS



### 70161

- 2 Units
- With Extension to 1/2"/1.2cm
- Tapped 0.2cm x 0.2cm
- Master Carton: 144
- Inner Pack: 6

## STANDARD BEADED CHAINS



### 70168

- Bronze Finish
- 2 Unidades
- Balls Diameter 1/8-IP/0.3cm
- Master Carton: 144
- Inner Pack: 6

## LOOPS



### 70155

- 2 2 Female Units
- Diameter 1" / 2.5cm
- Bronze Finish
- Thread 1/8-IP/0.3cm
- Master Carton: 144
- Inner Pack: 6

## SAFETY CAPS TO OUTLET



### 74321

- White Color
- Master Carton: 72
- Inner Pack: 6



### 74990

- Ivory Color
- Master Carton: 72
- Inner Pack: 6

## HARPS



### 70220

- Bronze Finish
- 2 Pieces
- 8"/20.3cm
- Master Carton: 72
- Inner Pack: 6

### 70222

- Bronze Finish
- 2 Pieces
- 10"/25.4cm
- Master Carton: 72
- Inner Pack: 6

### 70224

- Bronze Finish
- 2 Pieces
- 12"/30.4cm
- Master Carton: 72
- Inner Pack: 6

## FEED-THROUGH ON/OFF SWITCHES



### 70506

- Black Finish
- Use with N°18 Wire, SPT-1 Wire Only
- Master Carton: 72
- Inner Pack: 6



### 70500

- White Finish
- Use with N°18 Wire, SPT-1 Wire Only
- Master Carton: 72
- Inner Pack: 6

## COVERS

### 70065

- White Color
- White Color: 4 3/4"/12cm
- Spacing Screws: 3 1/2"/8.8cm
- Contents 2 Screws of:  
3/4" x 1/4"/1.9cm x 0.6cm
- Master Carton: 48
- Inner Pack: 4



## ELECTRIC CORDS

### 70108


- White Color
- Switch and Lampholder
- Base E14
- Polarized Plug
- Gauge 18-2
- Wire 105°
- Master Carton: 72
- Inner Pack: 6



## ELECTRIC CORDS

### 70105

- Golden Color
- 8 pies SPT-1
- Polarized Plug
- Gauge 18-2
- Wire 105°
- Separate and Free Ends
- Master Carton: 72
- Inner Pack: 6



## ELECTRIC CORDS

### 70100

- White Color
- 8 pies SPT-1
- Polarized Plug
- Gauge 18-2
- Wire 105°
- Separate and Free Ends
- Master Carton: 72
- Inner Pack: 6



## LAMP HOLDERS

### 70425

- Porcelain
- Standar Base
- 1/8"/0.3cm Thick
- Gauge 18
- Conductive 105°
- 60W 220V Height 2"/5cm
- Master Carton: 72
- Inner Pack: 6



### 70403

- Keyless
- 2 Units
- Thread 1/8"/0.3cm
- Base E14
- Master Carton: 72
- Inner Pack: 6



### 70402

- Keyless
- 2 Units
- Thread 1/8"/0.3cm
- Base E14
- Adjust  
3 1/4" a 4 3/4"/8.2cm a 12cm
- Master Carton: 144
- Inner Pack: 6



## LAMP HOLDERS

### 70146

- Vertical
- Standard Base
- Fits in Hole of  
3/8" x 1/4" / 0.9cm x 0.6cm
- Master Carton: 72
- Inner Pack: 6



### 70145

- Horizontal
- Standard Base
- Fits in Hole of  
7/8" x 1/4" / 2.2cm x 0.6cm
- Master Carton: 72
- Inner Pack: 6



### 70407

- Keyless
- Standard Base
- Thread 1/8"/0.3cm
- Master Carton: 72
- Inner Pack: 6



### 70410

- Push Through Socket
- Standard Base
- On/Off
- Tapped 1/8"/0.3cm
- Master Carton: 72
- Inner Pack: 6



### 70412

- Turn Knob
- Standard Base
- On/Off 3-Ways
- Tapped 1/8"/0.3cm
- Master Carton: 72
- Inner Pack: 6



### 70409

- In Porcelain
- Standard Base
- Threaded Cap 1/8"/0.3cm
- Master Carton: 72
- Inner Pack: 6



## LAMP HOLDER KITS

### 70408

- Standard Base
- Threaded Cap 1/8"/0.3cm
- 1 Lampholder
- 1 Fiber Washer
- 1 Niple 1 1/8" x 1"
- 1 Screw Collar Loop
- 1 Locknut
- 1 Niple 1 1/8" x 2"
- Master Carton: 32
- Inner Pack: 6



### 70025

- Bottle Kit
- Standard Base
- Lampholder
- Hardware for Install
- Set 8 feet Cord - 18 Gauge
- Bottle Adapter
- Master Carton: 48
- Inner Pack: 4




## LAMP HOLDER KITS

### 70350

Screw Collar Loop Kit for Canopies with 1 1/16"/2.6cm Center Hole

- 1 Crossbar
- 1 Threaded Ring
- 2 Locknuts
- 1 Niple 3.1cm x 0.6cm
- 1 Reducer 0.9cm x 0.6cm
- 2 Mounting Screws 0.6cm x 1.2cm
- Master Carton: 72
- Inner Pack: 6



## LAMP HOLDER KITS

### 70269

- 10"/25.4cm Harp Brass Plated
- Lampholder
- Hardware for Install
- Set 8 feet Cord - 18 Gauge
- Button Shooting
- Master Carton: 72
- Inner Pack: 6



## LAMP HOLDER KITS 3 WAY

### 70268

- 10"/25.4cm Harp Brass Plated
- 3 Way Lampholder
- Hardware for Install
- Set 8 feet Cord - 18 Gauge
- Button Shooting
- Master Carton: 72
- Inner Pack: 6



## LAMP HOLDER KITS BOTTLE ADAPTERS

### 70266

- 10"/25.4cm Harp Brass Plated
- Lampholder
- Hardware for Install
- Set 8 feet Cord - 18 Gauge
- Button Shooting
- Master Carton: 72
- Inner Pack: 6



## GLASS SHADES

### 81242

- Satin Crimp
- Fitter: 2 1/4" / 5.7cm
- Height: 4 3/8" / 11.1cm
- Diameter: 5 1/2" / 14cm
- Master Carton: 12



### 81618

- Frosted
- Fitter: 3 1/4" / 8.2cm
- Height: 4 3/4" / 12cm
- Diameter: 5 3/8" / 13.6cm
- Master Carton: 40



### 81238

- Amber Swirl
- Fitter: 2 1/4" / 5.7cm
- Height: 5 1/4" / 13.3cm
- Diameter: 4" / 10.1cm
- Master Carton: 24



### 81617

- Clear
- Fitter: 3 1/4" / 8.2cm
- Height: 4 3/4" / 12cm
- Diameter: 3 3/8" / 9.2cm
- Master Carton: 40



### 81120

- Cappuccino
- Fitter: 2 1/4" / 5.7cm
- Height: 4 1/4" / 10.7cm
- Diameter: 6 7/8" / 17.4cm
- Master Carton: 24







# ELECTRICAL DEVICES

...

## TRANSFORMER DOORBELLS

### 76180

- 16 Volt, 10 Watt
- Master Carton: 24
- Inner Pack: 6



## DOORBELL BUTTONS

### 76157

- White Color
- With Light
- Size: 2 7/8" x 7/8" / 7.30cm x 2.2cm
- Master Carton: 24
- Inner Pack: 6



## DOORBELL BUTTONS

### 76106

- Bronze Rim
- With Light
- Diameter: 3/4" / 2cm
- Master Carton: 24
- Inner Pack: 6



## CHIME KITS

### 76205

- White Geometric Design Chime
- One Lighted Gold Doorbell Button
- One Non-Lighted White Doorbell Button
- Transformador de 10W 16 Volts
- Size: 7 1/8" x 4" x 2" / 18cm x 10cm x 5cm
- Master Carton: 20





# LIGHT BULBS

Products Available in 120 V- / 220 V-, 50 Hz / 60 Hz





# FLUORESCENT LIGHT BULBS

Products Available in 120 V~ / 220 V~, 50 Hz / 60 Hz



# FLUORESCENT LIGHT BULBS



## Mini Spiral T2

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
39556	9	40	Std.	9W Mini Spiral T2 DL 1pk	Day Light	6400	10000	510	82	97	Blister	1	21
39566	9	40	Std.	9W Mini Spiral T2 WW 1pk	Warm White	2700	10000	540	82	97	Blister	1	21
39557	11	50	Std.	11W Mini Spiral T2 DL 1pk	Day Light	6400	10000	650	82	102	Blister	1	21
39567	11	50	Std.	11W Mini Spiral T2 WW 1pk	Warm White	2700	10000	690	82	102	Blister	1	21
39560	11	50	Std.	11W Mini Spiral T2 DL 2pk	Day Light	6400	10000	650	82	102	Blister	2	21
39558	13	60	Std.	13W Mini Spiral T2 DL 1pk	Day Light	6400	10000	825	82	98	Blister	1	21
39568	13	60	Std.	13W Mini Spiral T2 WW 1pk	Warm White	2700	10000	850	82	98	Blister	1	21
39561	13	60	Std.	13W Mini Spiral T2 DL 2pk	Day Light	6400	10000	825	82	98	Blister	2	21
39570	13	60	Std.	13W Mini Spiral T2 WW 2pk	Warm White	2700	10000	850	82	98	Blister	2	21
39563	13	60	Std.	13W Mini Spiral T2 DL 4pk	Day Light	6400	10000	825	82	98	Blister	4	14
39559	15	75	Std.	15W Mini x T2 DL 1pk	Day Light	6400	10000	900	82	98	Blister	1	21
39569	15	75	Std.	15W Mini Spiral T2 WW 1pk	Warm White	2700	10000	950	82	98	Blister	1	21
39562	15	75	Std.	15W Mini Spiral T2 DL 2pk	Day Light	6400	10000	900	82	98	Blister	2	21
39571	15	75	Std.	15W Mini Spiral T2 WW 2pk	Warm White	2700	10000	950	82	98	Blister	2	21
39564	15	75	Std.	15W Mini Spiral T2 DL 4pk	Day Light	6400	10000	900	82	98	Blister	4	14
37708	19	100	Std.	19W Mini Spiral T2 DL 1pk	Day Light	6400	10000	1160	82	105	Blister	1	21
37702	19	100	Std.	19W Mini Spiral T2 WW 1pk	Warm White	2700	10000	1200	82	105	Blister	1	21
37705	19	100	Std.	19W Mini Spiral T2 DL 2pk	Day Light	6400	10000	1160	82	105	Blister	2	14
37709	23	115	Std.	23W Mini Spiral T2 DL 1pk	Day Light	6400	10000	1450	82	112	Blister	1	21
37703	23	115	Std.	23W Mini Spiral T2 WW 1pk	Warm White	2700	10000	1500	82	112	Blister	1	21
37706	23	115	Std.	23W Mini Spiral T2 DL 2pk	Day Light	6400	10000	1450	82	112	Blister	2	14
37710	26	130	Std.	26W Mini Spiral T2 DL 1pk	Day Light	6400	10000	1600	82	114	Blister	1	21
37704	26	130	Std.	26W Mini Spiral T2 WW 1pk	Warm White	2700	10000	1700	82	114	Blister	1	21
37707	26	130	Std.	26W Mini Spiral T2 DL 2pk	Day Light	6400	10000	1600	82	114	Blister	2	14





Full Spiral Base Std.



Full Spiral Base E14



13 W Base Std.



15 W Base Std.

## Full Spiral T2

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
37792	5	25	E14	5W Full Spiral DL 1pk	Day Light	6400	8000	225	80	100	Blister	1	21
37793	5	25	E14	5W Full Spiral WW 1pk	Warm White	2700	8000	225	80	100	Blister	1	21
37794	5	25	Std.	5W Full Spiral DL 1pk	Day Light	6400	8000	225	80	95	Blister	1	21
37795	5	25	Std.	5W Full Spiral WW 1pk	Warm White	2700	8000	225	80	95	Blister	1	21
37796	9	40	E14	9W Full Spiral DL 1pk	Day Light	6400	8000	450	80	100	Blister	1	21
37797	9	40	E14	9W Full Spiral WW 1pk	Warm White	2700	8000	450	80	100	Blister	1	21
37798	9	40	Std.	9W Full Spiral DL 1pk	Day Light	6400	8000	450	80	95	Blister	1	21
37799	9	40	Std.	9W Full Spiral WW 1pk	Warm White	2700	8000	450	80	95	Blister	1	21

## Color Mini Spiral T3

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
37823	13	60	Std.	13W Mini Spiral T3 Blue 1pk	Blue	---	8000	---	---	120	Blister	1	14
37824	13	60	Std.	13W Mini Spiral T3 Red 1pk	Red	---	8000	---	---	120	Blister	1	14
37825	13	60	Std.	13W Mini Spiral T3 Green 1pk	Green	---	8000	---	---	120	Blister	1	14
37826	13	60	Std.	13W Mini Spiral T3 Yellow 1pk	Yellow	---	8000	---	---	120	Blister	1	14
37827	13	60	Std.	13W Mini Spiral T3 Black Light 1pk	Black	---	8000	---	---	120	Blister	1	14

## Spiral Bug Light T3

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
37719	15	75	Std.	15W Spiral Bug Light 1pk	Yellow	---	8000	---	---	120	Blister	1	20



## High Power Spiral

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blister/Box	Master Carton
37669	32	160	Std.	32W Spiral DL 1pk	Day Light	6400	8000	1988	82	155	Blister	1	21
37653	32	160	Std.	32W Spiral WW 1pk	Warm White	2700	8000	1988	82	155	Blister	1	21
39551	42	150	Std.	42W Spiral DL 1pk	Day Light	6400	8000	2500	80	203	Box	1	10
39553	65	300	Std.	65W Spiral DL 1pk	Day Light	6400	8000	3900	80	257	Box	1	10

## 4U & 5U High Power

Item	Potency (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blister/Box	Master Carton
37880	85	Mogul	85w 4U T5 6400k 4700L Mogul Base	Day Light	6400	20000	4700	79	610	Box	1	10
37881	85	Mogul	85W 4U T5 2700K 4700L Mogul Base	Warm White	2700	20000	4700	79	1220	Box	1	10
37895	105	Mogul	105W 5U T5 6400K 5800L Mogul Base	Day Light	6400	20000	5850	79	1220	Box	1	10
37896	105	Mogul	105W 5U T5 2700K 5800L Mogul Base	Warm White	2700	20000	5800	79	1220	Box	1	10



14 W  
Base Std.



11 W  
Base Std.



7 W  
Base E12+Std.

## Mini A-Shape

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blister	Master Carton
37737	9	40	Std.	9W Mini A-Shape A15 DL 1pk	Day Light	6400	8000	390	82	136	Blister	1	20
37738	9	40	Std.	9W Mini A-Shape A15 WW 1pk	Warm White	2700	8000	400	82	136	Blister	1	20
38113	14	60	Std.	14W Mini A-Shape A19 DL 1pk	Day Light	6400	8000	700	82	136	Blister	1	20
38114	14	60	Std.	14W Mini A-Shape A19 WW 1pk	Warm White	2700	8000	710	82	136	Blister	1	20

## Mini Globe

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blister	Master Carton
37788	7	25	Std.	7W Mini Globo G19.5 DL 1pk	Day Light	6400	8000	360	82	108	Blister	1	21
37791	7	25	Std.	7W Mini Globo G19.5 WW 1pk	Warm White	2700	8000	360	82	108	Blister	1	21
39599	11	50	Std.	11W Mini Globo G19.5 DL 1pk	Day Light	6400	8000	480	82	108	Blister	1	20
37800	11	50	Std.	11W Mini Globo G19.5 WW 1pk	Warm White	2700	8000	550	82	108	Blister	1	20
37802	15	75	Std.	15W Mini Globo G25 DL 1pk	Day Light	6400	8000	750	82	114	Blister	1	20
37803	15	75	Std.	15W Mini Globo G25 WW 1pk	Warm White	2700	8000	750	82	114	Blister	1	20

## Mini Candle

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blister	Master Carton
39590	7	25	E12+Std.	7W Mini Vela with Adaptera DL 1pk	Day Light	6400	8000	305	82	133	Blister	1	20
37787	7	25	Std.	7W Mini Vela DL 1pk	Day Light	6400	8000	360	82	133	Blister	1	21
37790	7	25	Std.	7W Mini Vela WW 1pk	Warm White	2700	8000	360	82	133	Blister	1	21



11 W  
Base GU10



PAR30  
15 W  
Base Std.



PAR38  
23 W  
Base Std.

## Reflector GU10-MR16


Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
37832	11	50	GU10	11W MR16 DL 1pk	Day Light	6400	8000	400	82	70	Blister	1	40
37833	11	50	GU10	11W MR16 WW 1pk	Warm White	2700	8000	400	82	70	Blister	1	40

## Reflector PAR20, PAR30, BR38

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
37745	11	50	Std.	11W Reflector PAR20 DL 1pk	Day Light	6400	8000	500	82	121	Blister	1	20
37747	15	75	Std.	15W Reflector PAR30 DL 1pk	Day Light	6400	8000	710	82	139	Blister	1	8
37748	15	75	Std.	15W Reflector PAR30 WW 1pk	Warm White	2700	8000	710	82	139	Blister	1	8
37811	26	130	Std.	26W Reflector BR38 DL 1pk	Day Light	6400	8000	1300	82	139	Blister	1	8

## Reflector PAR38

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
37813	23	115	Std.	23W Reflector PAR38 DL 1pk	Day Light	6400	8000	1200	82	170	Blister	1	8
37812	23	115	Std.	23W Reflector PAR38 WW 1pk	Warm White	2700	8000	1200	82	170	Blister	1	8
37828	23	---	Std.	23W Reflector PAR38 Blue 1pk	Blue	---	8000	---	---	140	Blister	1	8
37829	23	---	Std.	23W Reflector PAR38 Red 1pk	Red	---	8000	---	---	140	Blister	1	8
37830	23	---	Std.	23W Reflector PAR38 Green 1pk	Green	---	8000	---	---	140	Blister	1	8
37831	23	---	Std.	23W Reflector PAR38 Yellow 1pk	Yellow	---	8000	---	---	140	Blister	1	8



## Circular Fluorescent

Item	Power (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Box/ Blisters	Master Carton
37711	20	75	4-Pin	20W Circular T5/Reemplazo	Day Light	6400	8000	1200	82	152	Blister	1	20
06015	22	---	4-Pin	Circular FC8T9/DL	Day Light	6400	8000	1320	65	203	Box	1	20
37701	22	75	Std.	22W Circular T5 con Adaptador	Day Light	6400	8000	1200	82	152	Blister	1	20
39550	22	75	Std.	22W Circular T5 con Adaptador	Day Light	6400	8000	1200	65	304	Blister	1	20
06025	32	---	4-Pin	Circular FC12T9/DL	Day Light	6400	8000	1920	65	304	Box	1	20

## Tubular T5 Mini Bi-Pin

Item	Power (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Sleeve	Master Carton
07008	54	Bi-Pin	F54T5 / 841 / HO	Day Light	4100	20000	5000	85	1168	Sleeve	6	24
07032	54	Bi-Pin	F54T5 / 850 / HO	Warm White	5000	20000	5000	85	1168	Sleeve	6	24

## Tubular T8 Bi-Pin

Item	Power (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Sleeve	Master Carton
37725	17	Bi-Pin	F17T8 / 765	Cold Light	4100	20000	900	79	610	Sleeve	---	25
37724	32	Bi-Pin	F32T8 / 765	Warm White	4100	20000	2400	79	1220	Sleeve	---	25
38130	32	Bi-Pin	F32T8 / 741	Warm White	6500	20000	2650	79	1220	Sleeve	---	25



# SERIES LED

## WHAT IS A LED?

LED stands for Light Emitting Diode from (Light Emitting Diode). Is a semiconductor diode which, when crossed by electric current, emits light.

## BENEFITS

- Is environmentally friendly, not contains mercury
- Low power consumption
- Longer life, up to 20 years
- Mayor eficincia light with lower temperature.
- Power On.
- Ideal for decorative lighting or general

## LED LIGHT BULBS

Products Available in 120 V- / 220 V-, 50 Hz / 60 Hz





LED Base GU5.3



LED Base GU10



LED Dimmable Base GU10



Reflector LED PAR20 Base Std.



Reflector LED PAR30 Base Std.

## LED GU5.3 (12 V~)

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
38184	7	35	GU5.3	7W LED GU5.3 WW 1pk	Warm White	3000	25000	350	80	50	Blister	1	100
38185	7	35	GU5.3	7W LED GU5.3 DL 1pk	Day Light	5000	25000	400	70	50	Blister	1	100

## LED GU10

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
38186	7	35	GU10	7W LED GU10 WW 1pk	Warm White	3000	25000	350	80	50.5	Blister	1	100
38187	7	35	GU10	7W LED GU10 DL 1pk	Day Light	5000	25000	400	70	50.5	Blister	1	100
38191	7	35	GU10	7W LED GU10 DimmableWW 1pk	Warm White	3000	35000	350	80	50.5	Blister	1	100
38190	7	35	GU10	7W LED GU5.3 Dimmable DL 1pk	Day Light	5000	35000	400	70	50.5	Blister	1	100

## LED PAR20, PAR30

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
38189	9	70	Std.	9W LED PAR20 WW 1pk	Warm White	3000	35000	700	80	88	Blister	1	25
38188	14	70	Std.	14W LED PAR30 WW 1pk	Day Light	3000	35000	1000	80	117	Blister	1	20



LED Candle  
Base E14



LED Candle  
Base Std.



LED Mini Globe  
Base Std.



LED A  
Base Std.

## LED MINI GLOBE

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
37866	2.5	25	Std.	2.5W LED MINI GLOBE WW 1pk	Warm White	3000	15000	180	70	---	Blister	1	21
38306	2.5	25	Std.	2.5W LED MINI GLOBE DL 1pk	Day Light	6400	15000	180	70	---	Blister	1	21

## LED A

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
38177	7	35	Std.	7W LED A WW 1pk	Warm White	3000	15000	500	70	---	Blister	1	21
38178	7	35	Std.	7W LED A DL 1pk	Day Light	6400	15000	500	70	---	Blister	1	21


## LED CANDLE

Item	Potency (watts)	Equivalence (watts)	Base	Abbreviation Code	Color of Light	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	CRI	Measures (mm)	Individual Packing	Pieces per Blisters	Master Carton
38183	3	27	E14	3W LED CANDLE WW 1pk	Warm White	3000	25000	210	80	---	Blister	1	21
38182	3	27	E14	3W LED CANDLE DL 1pk	Day Light	6400	25000	210	80	---	Blister	1	21
38181	3	27	Std.	3W LED CANDLE WW 1pk	Warm White	3000	25000	210	80	---	Blister	1	21
38180	3	27	Std.	3W LED CANDLE DL 1pk	Day Light	6400	25000	210	80	---	Blister	1	21

# INCANDESCENT

The incandescent bulb produces light by means of electrical heating wire (filament) at a high temperature that the radiation is emitted in the visible spectrum. They are the oldest known light sources with which you get the best color reproduction, with a light very close to natural sunlight.

## FILAMENT



INCANDESCENT  
LIGHT BULBS







## A15

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Volts	Measures (mm)	Individual Packing	Pieces per Blisters/Box	Inner Pack	Master Carton
04003	40	Std.	C9	40A15	Clear	2500	350	120	88	Box	1	10	60
04001	40	Std.	C9	40A15 / CD	Clear	1000	350	120	88	Blister	1	6	72
04002	40	Std.	C9	40A15 / F / CD	Frosted	1000	340	120	88	Blister	1	6	72
03998	60	Std.	C9	60A15 / 2	Clear	2500	570	120	88	Box	2	6	24

## A19

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Volts	Measures (mm)	Individual Packing	Pieces per Box	Inner Pack	Master Carton
03445	25	Std.	C9	25A / TB	Trans. Blue	2500	----	120	114	Box	1	4	36
03444	25	Std.	C9	25A / TG	Trans. Green	2500	----	120	114	Box	1	4	36
03446	25	Std.	C9	25A / TR	Trans. Red	2500	----	120	114	Box	1	4	36
03447	25	Std.	C9	25A / TY	Trans. Yellow	2500	----	120	114	Box	1	4	36

## S11

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Light Center Length (Inch)	Volts	Measures (mm)	Individual Packing	Pieces per Blisters	Inner Pack	Master Carton
04064	17 1/2	Std.	C7A	7 1/2S11/CD	Clear	1500	53	1 5/8"	120	57	Blister	2	10	120

## C7

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Light Center Length (Inch)	Volts	Measures (mm)	Individual Packing	Pieces per Blisters	Inner Pack	Master Carton
03794	4	Cand.	C7A	4C7 / CD2	Clear	3000	20	1 3/16"	120	53	Blister	2	10	120
04794	4	Cand.	C7A	4C7 / CD4	Clear	3000	20	1 3/16"	120	53	Blister	4	10	120
03691	7	Cand.	C7A	7C7	Clear	3000	45	1 3/16"	120	53	Box	1	10	120





## Flame Tip

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Light Center Length (Inch)	Volts	Measures (mm)	Individual Packing	Pieces per Blisters/Box	Inner Pack	Master Carton
03764	25	Std.	CC2V	25CA10 / CD2	Clear	1500	190	2 1/16"	120	107	Blister	2	10	60
03767	25	Std.	CC2V	25CA10 / F / CD2	Frosted	1500	175	2 1/16"	120	107	Blister	2	10	60
03774	25	Cand.	C7A	25CA8 / CD2	Clear	1500	175	1 3/4"	120	92	Blister	2	10	60
03778	25	Cand.	C7A	25CA8 / F / CD2	Frosted	1500	160	1 3/4"	120	92	Blister	2	10	60
03274	25	Cand.	C7A	25CA8	Clear	1500	190	1 3/4"	120	92	Blister	2	10	60
03278	25	Cand.	C7A	25CA8 / F	Frosted	1500	175	1 3/4"	120	92	Box	1	25	200
03765	40	Std.	CC2V	40CA10 / CD2	Clear	1500	365	2 1/16"	120	107	Blister	2	10	60
03768	40	Std.	CC2V	40CA10 / F / CD2	Frosted	1500	350	2 1/16"	120	107	Blister	2	10	60
03775	40	Cand.	C7A	40CA91/2 / CD2	Clear	2500	365	1 3/4"	120	100	Box	1	25	200
03779	40	Cand.	CC2V	40CA91/2 / F / CD2	Frosted	1500	350	1 7/8"	120	100	Blister	2	10	60
03275	40	Cand.	CC2V	40CA91/2	Clear	1500	365	1 7/8"	120	100	Box	1	25	200
03279	40	Cand.	CC2V	40CA91/2 / F	Frosted	1500	350	1 7/8"	120	100	Box	1	25	200
03762	60	Cand.	CC2V	60CA10 / CD2	Clear	1500	615	1 15/16"	120	107	Blister	2	10	60

## G16 1/2

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Light Center Length (Inch)	Volts	Measures (mm)	Individual Packing	Pieces per Box	Inner Pack	Master Carton
03838	25	Std.	CC2V	25G16 1/2	Clear	1500	160	1 3/4"	120	76	Box	1	10	200



# Torpedo

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Light Center Length (Inch)	Volts	Measures (mm)	Individual Packaging	Pieces per Blisters/Box	Inner Pack	Master Carton
03731	25	Std.	CC2V	25B11 / CD2	Clear	1500	190	2 1/16"	120	98	Blister	2	10	60
03734	25	Std.	CC2V	25B11 / F / CD2	Frosted	1500	175	2 1/16"	120	98	Blister	2	10	60
03231	25	Std.	CC2V	25B11	Clear	1500	190	2 1/16"	120	98	Box	1	25	200
03782	25	Cand.	CC2V	25B91/2 / CD2	Clear	1500	190	1 7/8"	120	88	Blister	2	10	60
03785	25	Cand.	CC2V	25B91/2 / F / CD2	Frosted	1500	175	1 7/8"	120	88	Blister	2	10	60
03285	25	Cand.	CC2V	25B91/2 / F	Frosted	1500	175	1 7/8"	120	88	Box	1	25	200
03341	25	E14S	CC2V	25B91/2 / CD2	Clear	2500	170	2 1/16"	130	88	Blister	2	10	60
40155	25	E14S	CC2V	25B91/2 / F / CD2	Frosted	2500	170	2 1/16"	130	88	Blister	2	10	60
03732	40	Std.	CC2V	40B11 / CD2	Clear	1500	365	2 1/16"	120	98	Blister	2	10	60
03735	40	Std.	CC2V	40B11 / F / CD2	Frosted	1500	350	2 1/16"	120	98	Blister	2	10	60
03783	40	Cand.	CC2V	40B91/2 / CD2	Clear	1500	365	1 7/8"	120	88	Blister	2	10	200
03786	40	Cand.	CC2V	40B91/2 / F / CD	Frosted	1500	350	1 7/8"	120	88	Blister	2	10	60
03283	40	Cand.	CC2V	40B91/2	Clear	1500	365	1 7/8"	120	88	Box	1	25	200
03342	40	E14S	CC2V	40B91/2 / CD2	Clear	2500	345	2 1/16"	130	88	Blister	2	10	60
40156	40	E14S	CC2V	40B91/2 / F / CD2	Frosted	2500	330	2 1/16"	130	88	Blister	2	10	60
03793	60	Std.	CC2V	60B11 / CD2	Clear	1500	615	2 1/16"	120	98	Blister	2	10	60
03796	60	Std.	CC2V	60B11 / F / CD2	Frosted	1500	590	2 1/16"	120	98	Blister	2	10	60
03343	60	E14S	CC2V	60B10 / CD2	Clear	2500	610	2 1/16"	130	98	Blister	2	10	60
03784	60	Cand.	CC2V	60B10 / CD2	Clear	1500	615	2"	120	95	Blister	2	10	60
03284	60	Cand.	CC2V	60B10	Clear	1500	615	2"	120	95	Box	1	25	200

**G25 White  
Base Std.**



**R20  
Base Std.**



**BR30  
Base Std.**



## G25

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Light Center Length (Inch)	Volts	Measures (mm)	Individual Packing	Pieces per Box	Inner Pack	Master Carton
03121	25	Std.	C9	25G25 / W	White	1500	180	2 15/16"	120	111	Box	1	12	72
03122	40	Std.	C9	40G25 / W	White	1500	340	2 15/16"	120	111	Box	1	12	72

## Reflector R20

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Volts	Measures (mm)	Individual Packing	Pieces per Box	Inner Pack	Master Carton
03695	50	Std.	CC6	50R20 / FL	Flood	2000	380	120	101	Box	1	6	36
03694	50	Std.	CC6	50R20 / SP	Spot	2000	280	120	101	Box	1	6	36

## Reflector BR30

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Hours of Life	Luminous Flux (Lumens)	Volts	Measures (mm)	Individual Packing	Pieces per Box	Inner Pack	Master Carton
03680	50	Std.	CC6	50BR30 / FL	Flood	2000	400	120	146	Box	1	6	36

# HALOGEN

They offer long life and energy efficiency compared to their incandescent counterparts. Halogen bulbs are available in different strengths and forms, including decorative household, and reflector lamps that provide dazzling bright white light. Encapsulated PAR bulbs longer compared to incandescent equivalents. Our PAR halogen bulbs are ideal for use in offices, conference rooms, lobbies, among others, and can add dramatic accent to any room in a house.



HALOGEN  
LIGHT BULBS

...



## MR11, MR16 Dichroic (Low Voltage)

Item	Power (watts)	Base	Filament	Abbreviation Code	Light Temp. (°Kelvin)	Hours of Life	Candle Power	Bream Spread	Volts	Measures (mm)	Individual Packing	Pieces per Blister	Inner Pack	Master Carton
04756	50	GU5.3	C8	50MR16Q / FL / CD	3050	2000	1500	36°	120	80	Blister	1	6	36

## MR16 Dichroic (Line Voltage)

Item	Power (watts)	Base	Filament	Abbreviation Code	Light Temp. (°Kelvin)	Hours of Life	Candle Power	Bream Spread	Volts	Measures (mm)	Individual Packing	Pieces per Blox	Inner Pack	Master Carton
04519	50	GU7.9/8.0	CC8	50MR16Q/FL/LN with Lens	3050	1500	1800	36°	120	48	Box	1	10	100
03031	50	GU10	CC2V	50MR16Q/GU10/FL/LN/CD with Lens	3050	1500	1800	36°	120	50	Box	1	6	36
03030	50	GU5.3	CC2V	50MR16Q/GX5.3/FL/LN/CD with Lens	3050	1500	1800	36°	120	50	Box	1	6	36

## G9

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	Volts	Measures (mm)	Individual Packing	Pieces per Blister	Inner Pack	Master Carton
04871	40	G9	CC8	40T4Q / G9 / 120 / CD	Claro	2750	2000	800	120	36	Blister	1	6	36
04879	60	G9	CC8	60T4Q / G9 / 120 / CD	Claro	2800	2000	780	120	36	Blister	1	6	36

## JC (Bajo Voltaje)

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	Volts	Measures (mm)	Individual Packing	Pieces per Blister	Inner Pack	Master Carton
04736	20	G4	C6	20T3 / CD	Claro	2950	2000	300	120	30	Blister	1	6	36





Double Ended Long  
Base RSC

## Double Ended Long

Item	Power (watts)	Base	Filament	Abbreviation Code	Finish	Light Temp. (°Kelvin)	Hours of Life	Luminous Flux (Lumens)	Volts	Measures (mm)	Individual Packing	Pieces per Blister	Inner Pack	Master Carton
04776	300	RSC	C8	300T3Q / CD	Claro	3000	1500	5950	120	119	Blister	1	6	36
04778	500	RSC	C8	500T3Q / CD	Claro	3050	1500	10500	120	119	Blister	1	6	36

## Encapsulated Reflector PAR20, PAR30, PAR38

Item	Power (watts)	Base	Filament	Abbreviation Code	Light Temp. (°Kelvin)	Hours of Life	Candle Power	Bream Spread	Volts	Measures (mm)	Individual Packing	Pieces per Box	Inner Pack	Master Carton
36910	50	Std.	CC8	50PAR20 / H / FL / 130 / 6	2500	550	1250	30°	130	83	Box	1	6	24
05420	50	Std.	CC8	50PAR20 / H / NFL	2000	550	2200	30°	120	83	Box	1	6	24
05423	50	Std.	CC8	50PAR30 / H / FL	2000	660	1350	35°	120	92	Box	1	6	24
05426	50	Std.	CC8	50PAR30 / H / FL / LN Long Neck	2000	660	1350	35°	120	119	Box	1	6	24
05435	75	Std.	CC8	75PAR30 / H / FL	2000	1100	2400	35°	120	91	Box	1	6	24
05427	75	Std.	CC8	75PAR30 / H / FL / LN Long Neck	2000	1100	2400	35°	120	119	Box	1	6	24
05211	75	Std.	CC8	75PAR30 / H / LN / FL	2500	990	3200	48°	120	120	Box	1	6	24
05470	45	Std.	CC8	45PAR38 / H / FL	2000	520	1700	30°	120	132	Box	1	---	12
05475	75	Std.	CC8	75PAR38 / H / FL	2000	1100	2400	30°	120	132	Box	1	---	12



FANS AND  
LIGHT FIXTURES  
FINISHES



## FANS AND LIGHTING FIXTURES FINISHES



Rustic Bronze



Brushed Aluminum



Textured Black



Iron



Brushed Bronze



Old Chicago



Ebony Bronze



Polished Brass



Matted Chrome



Chrome



Antique Brass



Satin Chrome



White



Titanium



Espresso





Antique Copper



Washed Copper



Antique Pewter



Matted Black



Brushed Nickel



Oil Rubbed  
Bronze



Textured White



Brushed Pewter



Sienna



INDEX AND CUBIC CAPACITY

...



# INDEX AND CUBIC CAPACITY

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
03030	0.12	0.0073	123
03031	0.14	0.0083	123
03121	0.1	0.071	121
03122	0.21	0.0349	121
03231	0.03	0.0351	120
03274	0.01	0.0199	119
03275	0.02	0.0046	119
03278	0.04	0.0195	119
03279	0.02	0.0277	119
03283	0.02	0.0042	120
03284	0.02	0.0351	120
03285	0.02	0.0042	120
03341	0.1	0.0248	120
03342	0.1	0.0238	120
03343	0.05	0.045	120
03444	0.07	0.0199	118
03445	0.07	0.0208	118
03446	0.07	0.0202	118
03447	0.05	0.0196	118
03680	0.31	0.0561	121
03691	0.02	0.0017	118
03694	0.17	0.0194	121
03695	0.14	0.0195	121
03731	0.15	0.026	120
03732	0.15	0.0259	120
03734	0.15	0.0258	120
03735	0.15	0.2589	120
03762	0.1	0.0232	119
03764	0.15	0.0245	119
03765	0.15	0.0245	119
03767	0.15	0.0255	119
03768	0.15	0.274	119
03774	0.09	0.0205	119
03775	0.1	0.023	119
03778	0.1	0.02	119
03779	0.1	0.0227	119
03782	0.1	0.0233	120
03783	0.1	0.023	120
03784	0.1	0.0233	120
03785	0.1	0.023	120
03786	0.09	0.0238	120
03793	0.15	0.026	120
03794	0.05	0.0075	120
03796	0.15	0.026	120

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
03998	0.18	0.0179	118
04001	0.11	0.0204	118
04002	0.1	0.0193	118
04003	0.1	0.0125	118
04064	0.07	0.0125	118
04519	0.11	0.0074	123
04736	0.03	0.0022	123
04776	0.06	0.0039	124
04778	0.06	0.0049	124
04794	0.09	0.0136	118
04871	0.06	0.0072	123
04879	0.06	0.0053	123
05211	0.58	0.0476	124
05420	0.25	0.0181	124
05423	0.49	0.0352	124
05426	0.58	0.0448	124
05427	0.6	0.0458	124
05435	0.74	0.0352	124
05470	0.87	0.0852	124
05475	0.92	0.0783	124
06015	0.47	0.0704	113
06025	0.67	0.1417	113
07008	0.39	0.0288	113
07032	0.39	0.0288	113
36910	0.29	0.0171	124
37653	0.33	0.0489	110
37669	0.37	0.0529	110
37701	0.51	0.0855	113
37702	0.29	0.0653	108
37703	0.31	0.0643	108
37704	0.29	0.0427	108
37705	0.44	0.0865	108
37706	0.44	0.0865	108
37707	0.51	0.0752	108
37708	0.29	0.0641	108
37709	0.31	0.0682	108
37710	0.31	0.0689	108
37711	0.36	0.0591	113
37719	0.2	0.03	109
37724	0.49	0.0413	113
37725	0.26	0.0216	113
37737	0.21	0.0395	111
37738	0.21	0.0402	111
37745	0.35	0.0436	112

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
37747	0.68	0.0841	112
37748	0.68	0.0871	112
37787	0.21	0.0389	111
37788	0.23	0.0748	111
37790	0.2	0.389	111
37791	0.23	0.0709	111
37792	0.2	0.03	109
37793	0.17	0.0207	109
37794	0.18	0.0228	109
37795	0.18	0.0228	109
37796	0.18	0.0228	109
37797	0.49	0.0413	109
37798	0.26	0.0216	109
37799	0.11	0.0143	109
37800	0.21	0.0469	111
37802	0.33	0.0602	111
37803	0.33	0.0601	111
37811	0.78	0.1714	112
37812	0.98	0.1341	112
37813	0.98	0.1332	112
37823	0.29	0.0458	109
37824	0.19	0.0462	109
37825	0.24	0.0499	109
37826	0.19	0.0305	109
37827	0.19	0.0308	109
37828	0.98	0.1314	112
37829	0.98	0.1312	112
37830	0.95	0.1312	112
37831	0.95	0.1349	112
37832	0.17	0.0197	112
37833	0.17	0.0198	112
37866	---	---	116
37880	1.06	0.1352	110
37881	1.06	0.1352	110
37895	1.21	0.1352	110
37896	1.21	0.1352	110
38113	0.26	0.0415	111
38114	0.26	0.0421	111
38120	5.68	0.6659	65
38121	5.79	0.6636	65
38122	5.62	0.6612	65
38123	6.06	0.6761	65
38124	7.5	0.872	65
38125	7.5	0.8511	65

# INDEX AND CUBIC CAPACITY

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
38124	7.5	0.872	65
38125	7.5	0.8511	65
38126	8.05	0.8575	65
38130	0.47	0.0406	113
38177	---	---	116
38178	---	---	116
38180	---	---	116
38181	---	---	116
38182	---	---	116
38183	---	---	116
38184	---	---	115
38185	---	---	115
38186	---	---	115
38187	---	---	115
38188	---	---	115
38189	---	---	115
38190	---	---	115
38191	---	---	115
38306	---	---	116
39550	0.63	0.0929	113
39551	0.63	0.0725	110
39553	0.76	0.1007	110
39556	0.18	0.024	108
39557	0.2	0.0417	108
39558	0.21	0.0467	108
39559	0.21	0.0443	108
39560	0.33	0.0454	108
39561	0.36	0.071	108
39562	0.39	0.0664	108
39563	0.66	0.1177	108
39564	0.7	0.127	108
39566	0.2	0.078	108
39567	0.16	0.027	108
39568	0.2	0.044	108
39569	0.21	0.0441	108
39570	0.32	0.0532	108
39571	0.33	0.0481	108
39590	0.24	0.0373	111
39599	0.21	0.0478	111
40155	0.1	0.0238	120
40156	0.1	0.023	120
64014	0.95	0.1497	78
64015	1.2	0.1501	78
64016	0.92	0.1609	78

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
64022	3.15	0.2466	76
64023	3.15	0.2466	76
64024	3.15	0.2466	76
64025	3.15	0.2466	76
64032	0.97	0.1122	80
64033	0.93	0.0986	80
64034	1.95	0.2266	80
64035	1.88	0.2151	80
64036	2.98	0.3952	80
64037	2.9	0.3952	80
64130	0.66	0.0642	84
64131	0.49	0.0642	84
64132	0.49	0.0642	84
64139	1.38	0.1727	83
64140	1.38	0.1727	83
64141	0.55	0.0642	84
64142	0.55	0.0642	84
64143	0.55	0.0642	84
64144	0.55	0.0642	84
64149	0.55	0.0642	84
64150	2.18	0.1517	94
64151	2.15	0.1517	94
64152	2.45	0.2184	94
64290	3.73	0.56	63
64291	3.73	0.56	63
64292	6.55	1.1369	63
64300	4.73	0.8134	62
64301	6.75	1.0814	62
64302	5.1	0.8009	64
64304	3.73	0.6129	62
64305	4.9	0.8009	62
64306	6.65	1.0903	62
64307	3.37	0.5771	63
64308	4.63	0.8067	63
64309	6.6	1.0666	63
64325	3.6	0.6101	64
64448	1.52	0.1737	86
64449	1.55	0.1721	86
64452	4	0.3565	86
64453	4.07	0.3552	86
64482	1.48	0.1737	86
64483	4.17	0.3565	86
64617	2.65	0.4891	74
64629	3.3	0.7735	68

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
64631	3.3	0.7733	68
64669	2.13	0.276	68
64671	2.07	0.2846	68
64683	4.87	0.6165	90
64687	2.17	0.1861	92
64691	3.7	0.5109	90
65606	0.97	0.0136	50
65608	1.93	0.0262	50
65659	0.97	0.0136	50
65661	0.97	0.0136	50
65682	1.93	0.0262	50
66055	5	0.8098	64
66069	3.93	0.5829	64
66095	4.67	0.8183	64
66097	1.62	0.1788	91
66119	0.66	0.0803	83
66120	1	0.1465	83
66122	1.26	0.2474	83
66123	2.45	0.3481	82
66124	1.74	0.2231	82
66125	1.98	0.2108	82
66126	2.45	0.2675	82
66127	1.69	0.1421	82
66129	2.49	0.2278	82
66130	3	0.2493	82
66132	2.67	0.2598	82
66161	3.63	0.6478	64
66162	4.5	0.796	64
66166	1.57	0.1483	95
66201	2.17	0.2172	69
66203	2.92	0.3758	67
66206	2.38	0.2824	68
66263	2.1	0.208	69
66327	3.37	0.5806	64
66329	2.07	0.2849	68
66373	1.28	0.1281	72
66374	3.5	0.5216	72
66375	1.83	0.2705	72
66376	3.23	0.6509	72
66378	3.43	0.5837	62
66401	1.48	0.1145	75
66402	2.34	0.1936	75
66403	2.12	0.2179	75
66406	2.07	0.1494	75

# INDEX AND CUBIC CAPACITY

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
66448	3.67	0.3328	75
66494	2.47	0.2969	74
66496	1.8	0.3734	74
66594	2.27	0.1494	75
66600	1.42	0.2658	69
66601	1.3	0.1615	75
66604	2.05	0.2773	67
66607	1.43	0.252	69
66610	3.53	0.4678	67
66611	2.5	0.4619	67
66654	1.35	0.1606	75
66677	1.63	0.2585	69
66679	1.93	0.2633	69
66681	1.73	0.2773	67
66683	1.6	0.1938	74
66685	2.53	0.3232	74
66692	1.8	0.2599	69
66698	3.57	0.4622	67
66699	1.6	0.2784	67
66800	1.57	0.1439	91
66803	1.4	0.2464	95
66822	2.83	0.281	88
66823	4.37	0.4758	88
66826	3.53	0.5039	90
66828	3.6	0.4969	90
66839	1.78	0.1882	91
66840	1.48	0.2566	88
66859	1.47	0.2202	92
66860	2.27	0.4781	92
66878	1.62	0.1788	91
66879	2.77	0.3797	95
66881	2.73	0.3857	95
66885	1.63	0.184	91
66898	2.13	0.2714	93
66919	1.52	0.1361	88
66945	1.5	0.252	95
66946	2.27	0.4688	92
66961	2.05	0.2652	93
66962	2.15	0.2644	93
66971	1.78	0.1921	93
66972	1.75	0.1947	93
66974	1.53	0.1493	91
66975	2.9	0.2658	88
66976	4.37	0.4708	88

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
66983	2.15	0.188	92
66984	2.15	0.188	92
67142	5.27	0.9248	64
67179	1.25	0.1607	75
67199	2.17	0.2565	74
67209	2.25	0.2167	67
67211	3.2	0.3422	69
67334	7.07	1.1556	66
67347	7.47	1.1882	66
67352	1.73	0.2012	71
67353	3.2	0.4284	71
67354	3.2	0.4412	72
67355	---	---	72
67356	4.1	0.4432	71
67357	1.67	0.2284	71
67358	3.53	0.4458	68
67363	1.68	0.2284	71
67364	4	0.4432	71
67378	7	1.0327	66
67418	3.87	0.4389	71
67419	2.47	0.2264	71
67831	3.9	0.5506	95
67834	4	0.571	95
67835	2.15	0.1474	94
67836	2.37	0.2111	94
67863	4.7	0.555	90
67864	4.7	0.555	90
67875	7.07	1.1556	66
67889	2.2	0.2675	93
67972	2.03	0.1851	95
70025	0.6	0.0428	101
70033	0.3	0.042	97
70034	0.27	0.0367	98
70035	0.27	0.0367	98
70037	0.28	0.0372	98
70038	0.31	0.041	97
70052	0.34	0.0365	97
70053	0.33	0.0365	97
70056	0.33	0.0365	97
70059	0.34	0.0367	97
70065	0.17	0.0154	100
70070	0.38	0.0242	98
70071	0.38	0.0301	98
70100	0.28	0.0291	100

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
70105	0.26	0.028	100
70108	0.26	0.031	100
70113	0.08	0.0061	98
70114	0.14	0.0091	98
70145	0.12	0.0163	101
70146	0.11	0.0149	101
70161	0.04	0.0046	99
70168	0.09	0.0044	99
70220	0.33	0.0638	99
70222	0.36	0.055	99
70224	0.42	0.051	99
70255	0.06	0.0088	99
70266	0.76	0.0707	102
70268	0.7	0.0835	102
70269	0.73	0.0687	102
70270	0.47	0.0265	99
70350	0.26	0.0192	102
70402	0.21	0.0271	100
70403	0.11	0.0109	100
70407	0.1	0.0175	101
70408	0.26	0.0172	101
70409	0.21	0.0176	101
70410	0.14	0.0184	101
70412	0.15	0.0179	101
70425	0.17	0.0152	100
70500	0.05	0.0062	99
70506	0.05	0.0062	99
70603	0.11	0.0098	99
70661	0.07	0.0066	48
70670	0.39	0.0252	98
70671	0.39	0.03	98
72141	18.4	1.8584	13
72152	17	1.5614	20
72156	---	---	18
72174	16.4	1.0974	32
72175	16.4	1.0942	32
72186	12.6	0.7578	18
72280	18.2	1.6859	36
72281	18.2	1.6859	36
72384	18.8	1.62	12
72386	12.6	0.6181	15
72387	12.8	0.6211	16
72389	18.2	1.2421	22
72390	18.6	1.8714	14

# INDEX AND CUBIC CAPACITY

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
72392	18.6	1.7306	25
72394	---	---	30
72395	11.2	0.7555	30
72399	15.4	1.457	33
72400	16.6	1.431	33
72401	12.8	1.1577	33
72414	---	---	28
72502	---	---	15
72503	---	---	17
72517	14.2	0.8256	15
72558	---	---	34
72559	---	---	10
72700	12.6	1.5137	56
72701	12.9	1.4872	56
72702	12.6	1.5137	57
72703	12.8	1.8036	57
72704	10.5	1.2671	58
72705	10	2.0002	54
72706	10.1	2.0669	54
72707	---	---	58
72708	---	---	53
72709	---	---	53
72710	---	---	53
72712	---	---	58
72713	10.5	1.5572	54
72714	15	1.8816	59
72715	---	---	55
72716	---	---	55
72717	---	---	55
74321	0.09	0.0201	99
74990	0.09	0.0208	99
76106	0.09	0.005	105
76157	0.04	0.0079	105
76180	0.96	0.0392	105
76205	2	0.0705	105
77006	0.06	0.0051	49
77007	0.07	0.006	48
77008	0.1	0.006	49
77013	0.07	0.006	48
77014	0.07	0.006	48
77019	0.04	0.006	49
77021	0.07	0.0064	47
77023	---	---	47
77039	0.07	0.0051	49

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
77049	0.06	0.0036	47
77050	0.06	0.0036	47
77051	0.03	0.0036	47
77052	---	---	47
77059	0.42	0.0347	46
77060	0.89	0.075	46
77064	0.06	0.0036	47
77075	0.1	0.0094	47
77084	0.13	0.0065	49
77087	0.11	0.006	48
77088	0.08	0.0078	49
77090	0.17	0.0125	47
77091	0.13	0.012	47
77092	0.34	0.0125	47
77095	0.11	0.0065	48
77105	1.21	0.304	44
77108	0.08	0.0051	49
77128	0.13	0.0081	49
77130	0.07	0.0097	49
77134	0.13	0.0053	49
77150	0.34	0.0367	45
77152	0.34	0.0367	45
77155	0.42	0.0467	45
77157	0.42	0.0483	45
77203	2.01	0.48	45
77215	0.08	0.0051	49
77224	0.06	0.0044	48
77225	0.06	0.0044	48
77238	0.06	0.0043	47
77240	0.59	0.0108	50
77241	0.58	0.01	50
77242	0.59	0.0108	50
77243	1.17	0.0192	50
77244	1.17	0.0196	50
77245	1.17	0.0204	50
77246	1.71	0.0279	50
77247	1.71	0.0271	50
77248	1.75	0.0279	50
77249	0.87	0.0141	50
77251	0.88	0.0141	50
77252	1.73	0.0271	50
77253	1.88	0.0267	50
77254	1.88	0.0279	50
77262	0.88	0.0163	50

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
77263	0.92	0.0138	50
77268	0.89	0.075	46
77302	2	0.475	45
77304	2.02	0.4475	45
77305	0.88	0.4767	45
77401	1.3	0.1313	46
77402	0.8	0.0596	46
77406	1.63	0.1292	46
77407	1.59	0.1296	46
77410	2.77	0.137	46
77411	2.68	0.137	46
77415	3.4	0.168	46
77416	3.27	0.1728	46
77509	0.85	0.0117	50
77510	1.68	0.0217	50
77515	0.99	0.0118	50
77516	1.76	0.0224	50
77526	0.99	0.0118	50
77527	1.76	0.0226	50
77550	0.26	0.0183	48
77582	0.99	0.0118	50
77620	0.15	0.0138	48
77621	0.15	0.0132	48
77635	0.11	0.0085	49
77639	0.11	0.0108	48
77870	0.88	0.0891	44
77871	0.51	0.0843	44
77872	0.61	0.1061	44
77873	0.64	0.0928	44
77875	0.84	0.1119	44
78009	19	1.6106	12
78016	18.8	1.6106	11
78017	19	1.8284	11
78023	13	0.6278	16
78024	16.4	1.2427	26
78042	18	1.2512	23
78079	20.4	1.7142	24
78108	11.6	0.7514	30
78112	27.8	2.9963	21
78123	11.4	0.6617	28
78126	11.6	0.6548	28
78127	16.6	1.089	33
78133	10.6	0.6702	27
78136	18.4	1.7027	12

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
78144	12.6	0.6267	17
78145	13.4	0.6174	17
78146	13.6	0.934	28
78170	12	0.9152	30
78181	---	---	11
78209	18.4	1.8782	14
78248	12.6	0.6134	16
78268	14.2	1.1875	26
78293	21.2	1.7927	10
78314	18.6	1.7306	25
78374	18.6	1.744	25
78391	18.2	1.7334	25
78400	---	---	20
78432	20.6	1.7039	24
78433	18.2	1.2275	23
78434	17.8	1.2471	22
78449	10	0.616	27
78508	13.4	1.0305	27
78521	20.4	1.7048	24
78556	---	---	10
78567	21	1.8991	24
78568	20.4	1.7262	23
78569	18.4	1.9075	13
78583	18.8	1.919	14
78610	20	2.0381	21
78611	18.8	1.7233	12
78612	18.8	1.8763	14
78613	18.2	1.2471	22
78614	16.6	1.1106	32
78615	12.6	1.0328	27
78623	---	---	32
78627	18.2	1.2365	22
78629	12.8	0.6134	17
78657	9.5	0.5679	29
78658	9.5	0.5763	29
78669	11.9	0.9244	29
78671	12.1	0.9193	29
78673	14.4	0.7003	18
78676	12.4	0.6253	18
78677	20.4	1.9724	21
78678	18.4	1.2713	23
78680	17	1.2506	34
78685	16.8	1.665	10
78711	16.8	1.3005	21

Item #	Weight In Pounds (lb)	Cubic Feet (ft <sup>3</sup> )	Page
78712	18	1.7079	13
78713	---	---	16
78714	19	1.4507	26
78724	20.1	2.3821	20
78767	19.4	2.4408	15
78772	14.2	1.185	26
78799	19.8	1.9981	20
78992	---	---	11
78993	---	---	13
81120	1.32	0.0705	103
81238	0.7	0.0534	103
81242	0.63	0.0826	103
81617	0.88	0.0477	103
81618	0.93	0.0544	103









**Westinghouse Lighting Latin America**  
Licensee Westinghouse Electric Corporation

 WESTINGHOUSE • INNOVATION YOU CAN BE SURE OF  
are trademarks of Westinghouse Electric Corporation.  
Used under license. All Rights Reserved.

[www.wl-la.com](http://www.wl-la.com)