

Lighting Selections



FINE LINE
homes



P4490-20 Antique Bronze
Five-light chandelier with fluted, Etched light
umber glass shades
Size: Ht: 18-7/8", W 24"
Lamps(s): Five Medium Base, each 100W max.



P4490-09 Brushed Nickel
Five-light chandelier with fluted, etched white glass
Size: Ht: 18-7/8", W 24"
Lamps(s): Five Medium Base, each 100W max.



P4492-20 Antique Bronze
Nine-light two tier chandelier
Size: Ht: 27 3/4", W 28"
Lamps(s): Nine Medium Base, each 100W max.



P4492-09 Brushed Nickel
Nine-light two tier chandelier
Size: Ht: 27 3/4", W 28"
Lamps(s): Nine Medium Base, each 100W max.



P4490-20 Antique Bronze
Five-light chandelier with fluted, Etched light
umber glass shades
Size: Ht: 18-7/8", W 24"
Lamps(s): Five Medium Base, each 100W max.



P4490-09 Brushed Nickel
Five-light chandelier with fluted, etched white glass
Size: Ht: 18-7/8", W 24"
Lamps(s): Five Medium Base, each 100W max.



P3855-20 Antique Bronze
Two-light semi-flush with modern trumpet glass shade
Size: Ht:9-5/8", W 13-3/8"
Lamps(s): Two Medium Base, each 100W max.



P3855-09 Brushed Nickel
Two-light semi-flush with modern trumpet glass shade
Size: Ht:9-5/8", W 13-3/8"
Lamps(s): Two Medium Base, each 100W max.



P4489-20 Antique Bronze
Three-light chandelier with fluted, Etched light
umber glass shades
Size: Ht: 16-3/8", W 20"
Lamps(s): Three Medium Base, each 100W max.



P4489-09 Brushed Nickel
Three-light chandelier with fluted, Etched light
umber glass shades
Size: Ht: 16-3/8", W 20"
Lamps(s): Three Medium Base, each 100W max.



P3926-20EUL Antique Bronze
Three-light close-to-ceiling fixture
Size: Ht: 6-5/8", W 15 1/4"
Lamps(s): Three Medium Base, each 60W max.



P3926-09 Brushed Nickel
Three-light close-to-ceiling fixture
Size: Ht: 6-5/8", W 15 1/4"
Lamps(s): Three Medium Base, each 60W max.



P5270-20 Antique Bronze
One-light mini-pendant
Size: Ht: 7", W 6"
Lamps(s): One Medium Base, each 100W max.



P5270-09 Brushed Nickel
One-light mini-pendant
Size: Ht: 7", W 6"
Lamps(s): One Medium Base, each 100W max.



P3924-20EUL Antique Bronze
One-light close-to-ceiling fixture
Size: Ht: 5-1/2", W 11-3/8"
Lamps(s): One Medium Base, each 60W max.



P3924-09 Brushed Nickel
One-light close-to-ceiling fixture
Size: Ht: 5-1/2", W 11-3/8"
Lamps(s): One Medium Base, each 60W max.



P3925-20EUL Antique Bronze
Two-light close-to-ceiling fixture
Size: Ht: 5-7/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3925-09 Brushed Nickel
Two-light close-to-ceiling fixture
Size: Ht: 5-7/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3925-20EUL Antique Bronze
Two-light close-to-ceiling fixture
Size: Ht: 5-7/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3925-09 Brushed Nickel
Two-light close-to-ceiling fixture
Size: Ht: 5-7/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P4358-09 Brushed Nickel
Ten-light, two-tier chandelier in the timeless Americana collection with delicate arms, decorative center column and candelabra lamps.
Size: 26" w., 23" ht.
Lamp(s): Ten Candelabra Base lamp(s), each 60w max.



P4358-20 Antique Bronze
Ten-light, two-tier chandelier in the timeless Americana collection with delicate arms, decorative center column and candelabra lamps.
Size: 26" w., 23" ht.
Lamp(s): Ten Candelabra Base lamp(s), each 60w max.



P4359-09 Brushed Nickel
Fifteen-light, three-tier chandelier in the timeless Americana collection with delicate arms, decorative center column and candelabra lamps.
Size: 26" w., 27 3/4" ht.
Lamp(s): Fifteen Candelabra Base lamp(s), each 60w max.



P4359-20 Antique Bronze
Fifteen-light, three-tier chandelier in the timeless Americana collection with delicate arms, decorative center column and candelabra lamps.
Size: 26" w., 27 3/4" ht.
Lamp(s): Fifteen Candelabra Base lamp(s), each 60w max.



P3779-09 Brushed Nickel
Six-sided foyer fixture with clear, beveled glass panels. Hinged panel for ease of relamping.
Size: 12-1/4" w., 31-3/4" ht.
Lamp(s): Six Candelabra Base lamp(s), each 60w max.



P3779-20 Antique Bronze
Six-sided foyer fixture with clear, beveled glass panels. Hinged panel for ease of relamping.
Size: 12-1/4" w., 31-7/8" ht.
Lamp(s): Six Candelabra Base lamp(s), each 60w max.



P3927-20 Antique Bronze
Two-light close-to-ceiling
Size: Ht: 13-1/4", W 13-1/4"
Lamps(s): Two Medium Base, each 100W max.



P3927-09 Brushed Nickel
Two-light close-to-ceiling
Size: Ht: 13-1/4", W 13-1/4"
Lamps(s): Two Medium Base, each 100W max.



P4094-20 Antique Bronze
Three-light chandelier with clear prismatic glass shades
Size: Ht:12", W 19-3/4"
Lamps(s): Three Medium Base, each 100W max.



P4094-09 Brushed Nickel
Three-light chandelier with clear prismatic glass shades
Size: Ht:12", W 19-3/4"
Lamps(s): Three Medium Base, each 100W max.



P3818-20 Antique Bronze
Three-light close-to-ceiling with etched ribbed glass
Size: Ht: 7-1/2", W 15-1/4"
Lamps(s): Three Medium Base, each 75W max.



P3818-09 Brushed Nickel
Three-light close-to-ceiling with etched ribbed glass
Size: Ht: 7-1/2", W 15-1/4"
Lamps(s): Three Medium Base, each 75W max.



P3818-30 White
Three-light close-to-ceiling with etched ribbed glass
Size: Ht: 7-1/2", W 15-1/4"
Lamps(s): Three Medium Base, each 75W max.



P5096-09 Brushed Nickel
One-light mini-pendant.
Size: 6-1/2" w., 7" ht.
Lamp: One Medium Base
lamp 100w max.



P5096-20 Antique Bronze
One-light mini-pendant.
Size: 6-1/2" w., 7" ht.
Lamp: One Medium Base lamp
100w max.



P3816-20 Antique Bronze
One-light close-to-ceiling with etched ribbed glass
Size: Ht: 6", W 11-3/8"
Lamps(s): One Medium Base, each 75W max.



P3816-09 Brushed Nickel
One-light close-to-ceiling with etched ribbed glass
Size: Ht: 6", W 11-3/8"
Lamps(s): One Medium Base, each 75W max.



P3816-30 White
One-light close-to-ceiling with etched ribbed glass
Size: Ht: 6", W 11-3/8"
Lamps(s): One Medium Base, each 75W max.



P3817-20 Antique Bronze
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-09 Brushed Nickel
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-30 White
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-20 Antique Bronze
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-09 Brushed Nickel
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-30 White
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P4441-20 Antique Bronze
Five-light chandelier
Size: Ht: 15, W 20-1/2"
Lamps(s): Five Medium Base, each 100W max.



P4441-09 Brushed Nickel
Five-light chandelier
Size: Ht: 15, W 20-1/2"
Lamps(s): Five Medium Base, each 100W max.



P3914-20 Antique Bronze
Two-light Inverted pendant
Size: Ht: 20-5/8", W 15"
Lamps(s): Two Medium Base, each 100W max.



P3914-09 Brushed Nickel
Two-light Inverted pendant
Size: Ht: 20-5/8", W 15"
Lamps(s): Two Medium Base, each 100W max.



P4627-20 Antique Bronze
Nine-light, 2-tier chandelier
Size: Ht: 20-1/2", W 27-3/4"
Lamps(s): Nine Medium Base, each 100W max.



P4627-09 Brushed Nickel
Nine-light, 2-tier chandelier
Size: Ht: 20-1/2", W 27-3/4"
Lamps(s): Nine Medium Base, each 100W max.



P3929-20 Antique Bronze
Six-light foyer
Size: Ht: 24", W 15"
Lamps(s): Six Medium Base, each 60W max.



P3927-09 Brushed Nickel
Six-light foyer
Size: Ht: 24", W 15"
Lamps(s): Six Medium Base, each 60W max.



P3927-20 Antique Bronze
Two-light close-to-ceiling
Size: Ht: 13-1/4", W 13-1/4"
Lamps(s): Two Medium Base, each 100W max.



P3927-09 Brushed Nickel
Two-light close-to-ceiling
Size: Ht: 13-1/4", W 13-1/4"
Lamps(s): Two Medium Base, each 100W max.



P3818-20 Antique Bronze
Three-light close-to-ceiling with etched ribbed glass
Size: Ht: 7-1/2", W 15-1/4"
Lamps(s): Three Medium Base, each 75W max.



P3818-09 Brushed Nickel
Three-light close-to-ceiling with etched ribbed glass
Size: Ht: 7-1/2", W 15-1/4"
Lamps(s): Three Medium Base, each 75W max.



P3818-30 White
Three-light close-to-ceiling with etched ribbed glass
Size: Ht: 7-1/2", W 15-1/4"
Lamps(s): Three Medium Base, each 75W max.



P5113-20 Antique Bronze
One-light mini-pendant
Size: Ht: 5-3/4", W 4"
Lamps(s): One Medium Base, each 100W max.



P5113-09 Brushed Nickel
One-light mini-pendant
Size: Ht: 5-3/4", W 4"
Lamps(s): One Medium Base, each 100W max.



P3816-20 Antique Bronze
One-light close-to-ceiling with etched ribbed glass
Size: Ht: 6", W 11-3/8"
Lamps(s): One Medium Base, each 75W max.



P3816-09 Brushed Nickel
One-light close-to-ceiling with etched ribbed glass
Size: Ht: 6", W 11-3/8"
Lamps(s): One Medium Base, each 75W max.



P3816-30 White
One-light close-to-ceiling with etched ribbed glass
Size: Ht: 6", W 11-3/8"
Lamps(s): One Medium Base, each 75W max.



P3817-20 Antique Bronze
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-09 Brushed Nickel
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-30 White
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-20 Antique Bronze
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-09 Brushed Nickel
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P3817-30 White
Two-light close-to-ceiling with etched ribbed glass
Size: Ht: 6-1/8", W 13-1/4"
Lamps(s): Two Medium Base, each 75W max.



P4328-20 Antique Bronze
Five-light chandelier with etched glass.
Size: 23" w., 24" ht.
Lamp(s): Five Medium Base lamp(s), each 100w max.



P4328-09 Brushed Nickel
Five-light chandelier with etched glass.
Size: 23" w., 24" ht.
Lamp(s): Five Medium Base lamp(s), each 100w max.



P4324-20 Antique Bronze
Three-light chandelier with etched glass.
Size: 19" w., 21" ht.
Lamp(s): Three Medium Base lamp(s),
each 100w max.



P4324-09 Brushed Nickel
Three-light chandelier with etched glass.
Size: 19" w., 21" ht.
Lamp(s): Three Medium Base lamp(s),
each 100w max.



P4329-20 Antique Bronze
Nine-light chandelier with etched glass.
Size: 30" w., 33" ht.
Lamp(s): Nine Medium Base lamp(s), each 100w max.



P4329-09 Brushed Nickel
Nine-light chandelier with etched glass.
Size: 30" w., 33" ht.
Lamp(s): Nine Medium Base lamp(s), each 100w max.



P4328-20 Antique Bronze
Five-light chandelier with etched glass.
Size: 23" w., 24" ht.
Lamp(s): Five Medium Base lamp(s), each 100w max.



P4328-09 Brushed Nickel
Five-light chandelier with etched glass.
Size: 23" w., 24" ht.
Lamp(s): Five Medium Base lamp(s), each 100w max.



P3473-20 Antique Bronze
Two-light semi-flush close-to-ceiling fixture.
Size: 16" w., 15" ht.
Lamp(s): Two Medium Base lamp(s),
each 100w max.



P3473-09 Brushed Nickel
Two-light semi-flush close-to-ceiling fixture.
Size: 16" w., 15" ht.
Lamp(s): Two Medium Base lamp(s),
each 100w max.



P3477-20 Antique Bronze
Three-light close-to-ceiling fixture.
Size: 17" w., 9" ht.
Lamp(s): Three Medium Base lamp(s),
each 60w max.



P3477-09 Brushed Nickel
Three-light close-to-ceiling fixture.
Size: 17" w., 9" ht.
Lamp(s): Three Medium Base lamp(s),
each 60w max.



P5096-20 Antique Bronze
One-light mini-pendant.
Size: 6-1/2" w., 7" ht.
Lamp(s): One Medium Base lamp(s),
each 100w max.



P5096-09 Brushed Nickel
One-light mini-pendant.
Size: 6-1/2" w., 7" ht.
Lamp(s): One Medium Base lamp(s),
each 100w max.



P3475-20 Antique Bronze
One-light close-to-ceiling fixture.
Size: 12-1/2" w., 7-3/8" ht.
Lamp(s): One Medium Base lamp(s),
each 100w max.



P3475-09 Brushed Nickel
One-light close-to-ceiling fixture.
Size: 12-1/2" w., 7-3/8" ht.
Lamp(s): One Medium Base lamp(s),
each 100w max.



P3476-20 Antique Bronze
Two-light close-to-ceiling fixture.
Size: 15" w., 7-1/2" ht.
Lamp(s): Two Medium Base lamp(s),
each 60w max.



P3476-09 Brushed Nickel
Two-light close-to-ceiling fixture.
Size: 15" w., 7-1/2" ht.
Lamp(s): Two Medium Base lamp(s),
each 60w max.




P3476-20 Antique Bronze
Two-light close-to-ceiling fixture.
Size: 15" w., 7-1/2" ht.
Lamp(s): Two Medium Base lamp(s),
each 60w max.



P3476-09 Brushed Nickel
Two-light close-to-ceiling fixture.
Size: 15" w., 7-1/2" ht.
Lamp(s): Two Medium Base lamp(s),
each 60w max.

Standard Exterior Roman Coach Collection



P5767-31 Black



P5767-31 Black

FRONT ENTRANCE
P5767-20 Antique Bronze
Size: Ht: 19-1/4", W 7"
Lamps(s): One Medium Base, each 100W max.

SERVICE DOOR
P5762-20 Antique Bronze
Size: Ht: 9-7/8", W 6"
Lamps(s): One Medium Base, each 60W max.



P6417-31 Black



P5390-31PC Black
Aluminum post with photocell
Size 7' L, 3" W.

POST LIGHT (Optional)
P6417-20 Antique Bronze
Size: Ht: 22-5/8", W 9-5/8"
Lamps(s): One medium Base, each 60W max.



P5391-31PC Black
Aluminum post with photocell & ladder rest
Size 7' L, 3" W.



FRONT ENTRANCE
P5831-31 Black
 Size: Ht: 28-1/2", W 7-1/8"
 Lamps(s): One Medium Base, each 100W max.



SERVICE DOOR
P5758-31 Black
 Size: Ht: 18-3/4", W 5-3/8"
 Lamps(s): One Medium Base, each 100W max.



POST LIGHT (Optional)
P5432-31 Black
 Size: Ht: 21-3/4, W 9-3/4"
 Lamps(s): Three Candelabra Base, each 60W max.



P5390-31PC Black
 Aluminum post with photocell
 Size 7' L, 3" W.



P5391-31PC Black
 Aluminum post with photocell & ladder rest
 Size 7' L, 3" W.



P5863-30 White



P5863-31 Black

FRONT ENTRANCE
P5863-20 Antique Bronze
Size: Ht: 16", W 9"
Lamps(s): One Medium Base, each 100W max.



P5862-30 White



P5862-31 Black

SERVICE DOOR
P5862-20 Antique Bronze
Size: Ht: 12-3/4", W 6-7/8"
Lamps(s): One Medium Base, each 60W max.



P5434-30 White



P5434-31 Black

POST LIGHT (Optional)
P5434-20 Antique Bronze
Size: Ht: 19", W 11"
Lamps(s): One Candelabra Base, each 60W max.



P5390-31PC Black
Aluminum post with photocell
Size 7' L, 3" W.



P5391-31PC Black
Aluminum post with photocell & ladder rest
Size 7' L, 3" W.