

AT-A-GLANCE CATALOG

The Premium Choice in Landscape Lighting™

KICHLER
LIGHTING 

WWW.LANDSCAPELIGHTING.COM

KICHLER

A beautiful landscape starts with you.

Your vision. Your ideas. Kichler® technology. Together, there's nothing we can't do. From the latest, intelligent LED options to traditional incandescent choices, Kichler's complete landscape collection delivers exactly what you need. Leading the way is our Design Pro LED series of fixtures for virtually every outdoor application, including decorative path and spread, low profile hardscape, water feature, deck and accent lighting. You'll find our growing Design Pro LED line also offers the best of both form and function: every fixture is built to deliver beautiful, pure white natural lighting effects and is engineered for optimum all-weather performance. Of course, all Kichler fixtures offer installation-friendly features that add ease to the project without compromising performance.



Become a fan of Kichler Lighting at:
facebook.com
search Kichler Lighting



Follow us on
twitter.com/kichlerlight



Watch us on
youtube.com/KichlerLighting

Start with your ideas and let Kichler help bring them to light.

LOW VOLTAGE
**Design Pro LED
Path & Spread**

POWERED BY
**DESIGN PRO LED
TECHNOLOGY**



15807 AZT, BBR
LED 5.8 VA/4W

HIGH-LOW
SETTING



15801 TZT
LED 5.8 VA/4W



15843 CO, NBK, TZT, VG
LED 5.8 VA/4W



15871 BBR, TZT
LED 5.8 VA/4W

CAST
ALUMINUM
OR BRASS



15857 AZT
LED 5.8 VA/4W



15839 CO, TZT
LED 5.8 VA/4W



15850 CO
LED 5.8 VA/4W



15803 AZT
LED 5.8 VA/4W




15833 AZT
LED 5.9 VA/4W

LIGHTING
for
tomorrow
2010 Winner



15802 TZT
LED 5.8 VA/4W



15800 AZT, BBR
LED 5.8 VA/4W

HIGH-LOW
SETTING



15804 AZT
LED 5.9 VA/4W



8" SQUARE TOP

15806 BKT
LED 5.8 VA/4W



15817 AZT, BN
LED 5.8 VA/4W



HIGH-LOW SETTING

15827 BBR
LED 5.8 VA/4W



HIGH-LOW SETTING

15815 AZT, BE, BKT
LED 5.8 VA/4W



8.25" D x 21.25" H

15870 AZT, BBR, BE, BKT
LED 5.8 VA/4W



6" SQUARE TOP

15805 BKT
LED 5.8 VA/4W



8.25" D x 21" H

15810 AZT, BBR, BE, BKT
LED 5.8 VA/4W



8.25" D x 15" H

15811 AZT, BE
LED 5.8 VA/4W



15826 AZT, BE, BKT
LED 5.8 VA/4W

LOW VOLTAGE
Design Pro LED Deck & Patio

POWERED BY
DESIGN PRO LED TECHNOLOGY



15750 TZT
LED 2.4 VA/1.9W



15765 AZT, BBR, BE, BKT, WHT
LED 2.4 VA/1.9W



15763 TZT
LED 2.4 VA/1.9W



15764 AZT, BBR, WHT
LED 2.4 VA/1.9W



15773 AZT
LED 2.4 VA/3.8W



15774 AZT
LED 2.4 VA/3.8W



15782 AZT, BBR, BKT, CO, WHT
LED 2.4 VA/1.9W



15780 AZT
LED 2.4 VA/1.9W

LOW VOLTAGE
**Design Pro LED
 Hardscape,
 Deck, Step,
 Bench &
 Outdoor Kitchen**



15735 WHT
6.9" Length

15736 SD
12.9" Length

15755 AZT
18.9" Length

15735 AZT, BBR, CO, GRY, SD, WHT
LED 1.3 VA/.75W

15736 AZT, BBR, CO, GRY, SD, WHT
LED 3.7 VA/2.2W

15755 AZT, BBR, CO, GRY, SD, WHT
LED 2.4 VA/1.4W

15745 CO
6.9" Length

15746 GRY
12.9" Length

15756 BBR
18.9" Length

15745 AZT, BBR, CO, GRY, SD, WHT
LED 1.3 VA/.75W


15746 AZT, BBR, CO, GRY, SD, WHT
LED 2.4 VA/1.4W

15756 AZT, BBR, CO, GRY, SD, WHT
LED 3.7 VA/2.2W

LOW VOLTAGE
**Design Pro LED
 Accent**



15751 (10° spot) **15752 (35° flood)** **15753 (60° wide flood)**
 AZT, BBR, BKT LED 16.7 VA/12.4W



15731 (10° spot) **15732 (35° flood)** **15733 (60° wide flood)**
 AZT, BBR, BKT LED 7.5 VA/4.5W



15861 AZT, BBR, BKT
 LED 5.8 VA/4W



15741 (10° spot)
15742 (35° flood)
15743 (60° wide flood)
 AZT, BBR, BKT LED 12.2 VA/8.5W

LOW VOLTAGE
**Design Pro LED
 Well Lights**



15767 (10° spot), 15768 (35° flood), 15769 (60° wide flood) BKT LED 7.5 VA/4.5W



15728 (10° spot), 15747 (35° flood), 15748 (60° wide flood) BKT LED 12.2 VA/8.5W



15729 (10° spot), 15757 (35° flood), 15758 (60° wide flood) BKT LED 16.7 VA/12.4W

LOW VOLTAGE
**Design Pro LED
 2-in-1
 Water/Accent
 Light**



15711 SS
 LED 4.9 VA/3.4W

LOW VOLTAGE
Incandescent
Path & Spread



15379 OZ
24.4-W(VA) Bulb Included



15446 OZ
16.25-W(VA) Bulb Included



15447 OZ
11.6-W(VA) Bulb Included



15426 BKT
11.6-W(VA) Bulb Included



15449 TZT
11.6-W(VA) Bulb Included



15436 OZ
11.6-W(VA) Bulb Included



15347 VGB
24.4-W(VA) Bulb Included



15314 AZT, MST
24.4-W(VA) Bulb Included



15422 AGZ
11.6-W(VA) Bulb Included



15369 TZT
18.5-W(VA) Bulb Included



15393 OZ
11.6-W(VA) Bulb Included



15429 TZT
11.6-W(VA) Bulb Included



15307 CO
24.4-W(VA) Bulb Included



15437 TZT
16.25-W(VA) Bulb Included



15457 AZT
16.25-W(VA) Bulb Included



15420 AGZ
11.6-W(VA) Bulb Included



15421 AGZ
11.6-W(VA) Bulb Included



15330 OZ
24.4-W(VA) Bulb Included



15332 OZ
18.5-W(VA) Bulb Included



15324 PZ
24.4-W(VA) Bulb Included



15325 PZ
24.4-W(VA) Bulb Included



CAST ALUMINUM OR BRASS

15471 BBR, TZT
24.4-W(VA) Bulb Included



15358 OZ
16.25-W(VA) Bulb Included




15359 OZ
16.25-W(VA) Bulb Included



15401 TZT
20-W(VA) Bulb Included



15443 TZT, CO, NBK, OB, VG
15443 OB12 24.4-W(VA) Bulb Included



15373 BKT
18.5-W(VA) Bulb Included



15418 AZT
20-W(VA) Bulb Included



15458 OZ
11.6-W(VA) (2 required) Bulbs Included



15349 MST
18.5-W(VA) Bulb Included



15320 OZ
18.5-W(VA) Bulb Included



15313 TZG
16.25-W(VA) Bulb Included



15444 OZ
11.6-W(VA) Bulb Included




15453 AZT
11.6-W(VA) Bulb Included



15391 OZ
11.6-W(VA) Bulb Included



15392 OZ
11.6-W(VA) Bulb Included



15319 PZ
18.5-W(VA) Bulb Included

15365 CV
24.4-W(VA) Bulb Included



15430 CO
10-W(VA) Bulb Included



15431 CO
20-W(VA) Bulb Included



15322 AGZ
16.25-W(VA) Bulb Included



15455 CO
16.25-W(VA) Bulb Included



15351 CO
24.4-W(VA) Bulb Included



15350 CO
24.4-W(VA) Bulb Included



15367 TZT
24.4-W(VA) Bulb Included




15454 CO
11.6-W(VA) Bulb Included



15352 OZ
18.5-W(VA) Bulb Included



15438 CO, OB, OZ, VG
18.5-W(VA) Bulb Included




CASED GLASS



15435 AMB




15435 RD



15450 TZT
11.6-W(VA) Bulb Included

15435 PP
24.4-W(VA) Bulb Included




15334 OB
6.5-W(VA) Bulb Included



15317 AZT, BN
24.4-W(VA) Bulb Included



15318 AZT
24.4-W(VA) Bulb Included




15411 AZT, SA
16.25-W(VA) Bulb Included



15333 TZT
24.4-W(VA) Bulb Included



15360 AZT
24.4-W(VA) Bulb Included



15439 CO, OB, TZT
15439 OB6
24.4-W(VA) Bulb Included




15328 AZT
24.4-W(VA) Bulb Included



15005 AZT, BKT
24.4-W(VA) Bulb Included



15315 AZT, BE, BKT
15315 AZT6 24.4-W(VA)
Bulb Included




15326 AGZ, BE, BKT
15326 AZT6, 24.4-W(VA)
Bulb Included



15011 AZT, BKT
24.4-W(VA) Bulb Included



15336 BKT, TZT
24.4-W(VA) Bulb Included



15323 AZT, BKT, TZT
24.4-W(VA) Bulb Included




15423 AZT, BKT, TZT
24.4-W(VA) Bulb Included



15310 AZT, BE, BKT
15310 AZT6 16.25-W(VA)
Bulb Included



15410 AZT, BE
16.25-W(VA) Bulb Included



15470 AZT, BE, BBR, BKT
16.25-W(VA) Bulb Included

LOW VOLTAGE
Incandescent
Speciality



15409 oz
16.25-W(VA) (x4) Bulbs Included



15408 BKT
11.6-W(VA) (x6) Bulbs Included



15499 TZT
24.4-W(VA) Bulb Included



15415 TZT
16.25-W(VA) Bulb Included



15452 BW
6.5-W(VA) Bulb Included



15419 TZT
16.25-W(VA) Bulb Included



15123 BK
20-W(VA) Bulb Included



15402 oz
11.6-W(VA) (x9) Bulb Included

LOW VOLTAGE
Incandescent
Deck & Patio



15461 AZT
6.5-W(VA) Bulb Included



15063 OB, TZT
6.5-W(VA) Bulb Included



15050 TZT
6.5-W(VA) Bulb Included



15021 VGB
6.25-W(VA) Bulb Included



15469 TZT
6.5-W(VA) Bulb Included



15474 OZ
11.6-W(VA) Bulb Included



15110 OZ
4-W(VA) Bulb Included



15479 TZT
11.6-W(VA) Bulb Included



15071 OZ
11.6-W(VA) Bulb Included



15047 OZ
6.5-W(VA) Bulb Included



15462 BW
11.6-W(VA) Bulb Included



15064 AZT, BBR, BE, WHT
10-W(VA) Bulb Included



15065 AZT, BBR, BE, BKT, WHT
6.5-W(VA) Bulb Included



15079 AZT
11.6-W(VA) Bulb Included




Integral full back for mounting
on irregular surfaces.

15045 AZT
6.5-W(VA) Bulb Included



15468 AZT
6.5-W(VA) Bulb Included



15165 AZ
6.5-W(VA) Bulb Included




15077 AZT
18.5-W(VA) Bulb Included



15123 BK
20-W(VA) Bulb Included



15237 OB (120 V)
150-W(VA) Bulb Included



15066 AZT, WHT
6.5-W(VA) Bulb Included



15072 AZT, CO, WHT
11.6-W(VA) Bulb Included



15070 AZT
11.6-W(VA) Bulb Included



15073 AZT
10-W(VA) (2 required)
Bulb Included



15074 AZT
10-W(VA) (2 required)
Bulb Included

LOW VOLTAGE
**Incandescent
Accent**



15484 AZT
50-W(VA) MAX, 20-W(VA) MAX Canada



15397 AZT
50-W(VA) MAX, 35-W(VA) MAX Canada




15384 AZT, BBR, BKT, CO, MST
15384 AZT20L, AZT24
15384 BBR20L, BBR20L12
15384BKT24
50-W(VA) MAX, 20-W(VA) MAX Canada



15398 AZT
15398 BE20L
35-W(VA) MAX, 20-W(VA) MAX Canada



15309 AZT, BKT
15309 AZT12
20-W(VA) Bulb Supplied



15374 AZT, BKT, MST
15374 AZT20L, AZT20L24
15374 BE20L, BKT20L24
50-W(VA) MAX, 20-W(VA) MAX Canada




15390 AZT
50-W(VA) MAX



15382 BK
35-W(VA) MAX



15381 AZT, BBR, BKT
15381 AZT6
75-W(VA) MAX



15383 AZT
50-W(VA) Bulb Supplied



15395 AZT
50-W(VA) Bulb Supplied



15396 AZT
35-W(VA) Bulb Supplied



15385 AZT
50-W(VA) Bulb Supplied



15361 AZT, BKT
24.4-W(VA)



15363 BBR
24.4-W(VA)



15087 AZT
50-W(VA) MAX, 20-W(VA) MAX Canada




15093 WHT
50-W(VA) MAX, 20-W(VA) MAX Canada



15494 AZT
50-W(VA) MAX, 20-W(VA) MAX Canada

LOW VOLTAGE
Incandescent Well Lights



15488 BK
15488 BK12 35-W(VA) Bulb Supplied



15194 AZ
50-W(VA) MAX



15190 BK
50-W(VA) MAX, 20-W(VA) MAX Canada



15088 BK
15088 BK12 35-W(VA) MAX



15192 BK
50-W(VA) MAX, 10-W(VA) MAX Canada



15092 BKT
50-W(VA) MAX

LOW VOLTAGE
Incandescent Water Lights



15191 BK
50-W(VA) MAX, 20-W(VA) MAX Canada

LOW VOLTAGE
Accessories



Pro Series Connector 15529 BL



15570 AZT
15570 BBR
15570 BKT


Extends from
18" to 33"

Adjustable Height Stem



15671 ST

Bollard Template Kit




	.25" NPSM thd. Stems .50" D. overall	.50" NPSM thd. Stems .75" D. overall	.50" NPSM thd. Stems .75" D. overall
12"	15651 AZT 15651 BKT	6" 15645 AZT 15645 BBR 15645 BKT	18" 15657 AZT 15657 BBR 15657 BKT
18"	15652 AZT 15652 BKT	12" 15656 AZT 15656 BBR 15656 BKT	24" 15658 AZT 15658 BBR 15658 BKT
24"	15653 AZT 15653 BKT		

Fixture Mounting Stems



Bollard Mounting Kit



Bollard Mounting Stake



Polymetric Support Stakes



Elbow



Stem Coupler



Surface Mounting Flange



Flange Mounting Nipple



Tree/Surface Mounting Bracket



3 LED Flat Mounting Bracket



6 LED Flat Mounting Bracket



Out of Water Bracket



9 LED Flat Mounting Bracket



Multi-Fixture Weighted Base



Single Fixture Weighted Base



Junction Box Mounting Bracket



Three Fixtures, Centerpiece Mounting Kit




Incandescent Rock Guard



LED Well Light Rock Guard



Incandescent Well Light Rock Guard



45° Hexcell Louver Shield



Incandescent Blue Filters



INCANDESCENT
15672 FRO for use with fixture 15382
15676 FRO for use with fixtures
15092, 15384, 15484, 15494
15691 FRO for use with fixture 15381
15643 FRO for use with fixture 15374
15633 FRO for use with fixture 15398

LED
15895 FRO for use with fixtures 15731,
15732, 15733, 15741, 15742, 15743
15896 FRO for use with fixtures
15751, 15752, 15753

Frosted Lens



15677 CLR for use with
fixture 15327/15827
15695 CLR for use with
fixture 15315/15815
15696 CLR for use with fixture 15362

Polycarbonate Lens



15674 LIN clear ribbed for use
with fixture 15382
15675 LIN clear ribbed for use
with fixtures 15092, 15384, 15484, 15494
15692 LIN clear ribbed for use
with fixture 15381
15642 LIN clear ribbed for use
with fixture 15374
15632 LIN clear ribbed for use
with fixture 15398

Incandescent Linear Lens



Short Cowl
15701 AZTP/BKTP for use with
fixtures 15731, 15732, 15733,
15741, 15742, 15743
15702 AZTP/BKTP for use with
fixtures 15751, 15752, 15753
**For BBR fixture finishes,
use AZTP**

2.40"

Long Cowl
15703 AZTP/BKTP for use with
fixtures 15731, 15732, 15733,
15741, 15742, 15743
15704 AZTP/BKTP for use with
fixtures 15751, 15752, 15753
**For BBR fixture finishes,
use AZTP**

15703: 5.14"
15704: 6.0"

LED Snap-On Cowls



15875 AMB for use with
fixtures 15731, 15732, 15733,
15741, 15742, 15743
15876 AMB for use with
fixtures 15751, 15752, 15753

LED Amber Lens



15885 GRN for use with
fixtures 15731, 15732, 15733,
15741, 15742, 15743
15886 GRN for use with
fixtures 15751, 15752, 15753

LED Green Lens



15507 ONG

**Kichler Landscape
Flag Marker**



15659 AZT for use with fixture 15079
15689 BK for use with fixtures 15088, 15388

Heat Resistant Lens



12-gauge
15501 BK 100', 15502 BK 250'
15505 BK 500', 15506 BK 1000'
10-gauge 15504 BK 250'
8-gauge 15503 BK 250'

Low Voltage Cable



15579 BK for use when connecting:
• 8-gauge wire to 10- and 12-gauge
• connecting 10-gauge wire to 12-gauge wire

15589 BK for use when connecting:
• 10-gauge wire
• 12-gauge wire
• 10-gauge wire to 12-gauge wire
• 12-gauge wire to 18-gauge wire

Gel Filled Wire Connector



15509 BK for use with #12-2 or
#10-2 low voltage cable only

QUIC DISC® Connector

3" W.
3.09" H.
2.75" L



15557 BK

**Mechanical Transformer
Timer**

2.73" W.
3.84" H.
1.89" L



15556 WH

**Digital Transformer
Timer**



15534 BK
10' Cord

**Plug-In Transformer
Remote Photocell**



15565 BK

**Plug-In Transformer
Photocell**



15511 BK

Synchronizer Device



15670 BK

**Corrosion Preventive
Compound**

LOW VOLTAGE

Transformers

Power to perform:
Why Kichler® Transformers?

Kichler transformers are among the industry's very best in features, quality and conformity to ANSI/UL 1838 low voltage landscape lighting standards and recommended practices according to the National Electric Code. This selection guide can help you choose the perfect custom solution for the job.

SAFE

- Runs feature one common transformer per circuit. ANSI/UL1838 requirements limit each circuit to 300-W and 15V.
- Secondary circuit breakers offer short-circuit protection as a standard feature.
- Magnetic circuit breakers provide a faster response to a fault in the system.
- An in-line primary thermostat protects against thermal over-load. These built-in thermostats are auto-resetting, eliminating the need for replacement or maintenance.
- Because compliance and safety are important long after the installation is complete all Kichler Landscape Lighting low voltage transformers are listed or certified by UL, ETL, and/or CSA to the appropriate ANSI/UL 1838 standard for both the United States and Canada.

POWERFUL

- Various wattage options are available including: 60, 75, 100, 200, 300, 600, 900, and 1200 in many options.
- Available in premium or economy options – convenient for larger, more complicated jobs or where smaller profile, lower-wattage units can be used.

DURABLE

- Full enclosure of the housing protects components from weather, sprinkling systems and debris.
- Professional Series housings are made of stainless steel grade 304 designed to run cooler and resist corrosion, and last longer in outdoor environments.
- Multi-tap transformers allow greater flexibility in managing multiple wire runs by moving cables up and down the multi-range. This assures that the correct voltage is applied to a lamp – creating a consistent light output and maximizing lamp life.

WARRANTY

- Limited lifetime warranty offered on Stainless Steel (SS) transformer models.
- A limited 10-Year Warranty on powder-coated Textured Architectural Bronze (AZT) and Beach (BE) transformer models.



Wattage (VA)	Model #
75	15PR75 SS
100	15PR100 SS
200	15PR200 SS
300	15PR300 SS
600	15PRD600 SS
600	15PR600 SS
900	15PR900 SS
1200	15PR1200 SS

Professional Series



Wattage (VA)	Model #
100	15PL100 AZT
200	15PL200 AZT, BE
300	15PL300 AZT, BE
600	15PL600 AZT, BE
900	15PL900 AZT, BE

Plus Series



Wattage (VA)	Model #
300	15IG300 SS
600	15IG600 SS

In Ground



Wattage (VA)	Model #
100	15M100 AZT/BE
200	15M200 AZT/BE
300	15M300 AZT/BE
600	15M600 AZT/BE

Manual Series



Wattage (VA)	Model #
60	15E60 BK
120	15E120 BK

Economy

Design Pro LED



HARDSCAPE, DECK, STEP, BENCH & OUTDOOR KITCHEN LIGHTING

POWERED BY
DESIGN PRO LED
TECHNOLOGY

Discover LED like you've never seen it.

Unique and versatile LED light fixtures that are:

- Designed with a pure, warm, natural 2,950k white light
- Long-life 40,000 hour LED light source
- Tested to withstand the elements for years of enjoyment
- Easy to install
- Easily adapts to almost any hardscape, deck, step, bench or outdoor kitchen application
- Available finishes include Textured Architectural Bronze, Bronzed Brass, Copper, Gray, Sand and Textured White
- Finishes complement popular stone and decking options

For more information see our full line Landscape Lighting Catalog K211, or go to www.landscape-lighting.com, where you can also view complete warranty information.



KICHLER 
LIGHTING

KICHLER LIGHTING

World Headquarters
7711 E. Pleasant Valley Road • PO Box 318010
Cleveland, Ohio 44131-8010
www.landscape-lighting.com
220M/10-LD-1496. Catalog No. **K311**
Printed in USA. © Copyright All rights reserved. Kichler Lighting.



Become a fan of Kichler Lighting at:
[facebook.com](https://www.facebook.com/kichlerlighting)
search Kichler Lighting



Follow us on
twitter.com/kichlerlight



Watch us on
[youtube.com/KichlerLighting](https://www.youtube.com/KichlerLighting)

