

QUOIZEL®

Artisans in Lighting...since 1930

2016 - 2017

QUOIZEL.
Artisans in Lighting... since 1930



Welcome!

Our newest catalog is full of decorative lighting designed to help you enhance the beauty of your home. Our design team has been hard at work, and we hope that you enjoy our newest creations.

LED is the most exciting technology to impact Quoizel products. Its increased lumen output, energy efficiency and long life are three of the top benefits. As a result, the vast majority of our products are LED compatible and many of our new outdoor and bath fixtures now come with an integrated LED light source or LED bulbs. Check the product descriptions for specific information.

On behalf of the entire Quoizel family, thank you for making our products part of your home.

Sincerely,

A handwritten signature in blue ink that reads "Rick".

Rick Seidman
President / CEO

QUOIZEL

Since 1930, Quoizel has made it a practice to keep in step with evolving fashion trends in home décor and interior design around the world.

As an industry leader in home lighting for over 80 years, we at Quoizel repeatedly offer successful product lines ranging in style from traditional to contemporary, keeping hand-crafted artistry, cutting-edge innovation and enduring quality at our very core.

Our Board of Directors



Rick Seidman
President & CEO



Ira Phillips
Chairman of the Board



Toni Phillips
Executive Vice President



Todd Phillips
Executive Vice President



Ed Clark
Senior Vice President



Tim Hensch
Vice President/Operations

Our Locations



Charleston, SC



Hauppauge, NY

Follow **QUOIZEL** on social media:



Scan with your smart phone or tablet to view informative videos relating to our product line and catalog!



Tiffany



Mica



Pen, Shell



Agate, Stone



Onyx



Raffay

Guide to icons & reference codes



TRUCK ITEM



TITLE 20 COMPLIANT

All portable lamps shipped into the state of California will contain an energy-efficient fluorescent light bulb.



TITLE 24 COMPLIANT ENERGY-EFFICIENT

- 13W, 18W or 23W Compact Fluorescent Included
- CFL Spring Self-Ballasted GU 24

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying this logo. (Medium base bulbs only)



FIXTURE EXCEEDS 50 POUNDS



DIFFUSER INCLUDED



DAMP LOCATION



WET LOCATION



MOUNTS AS UPLIGHT OR DOWNLIGHT



MOUNTS VERTICALLY OR HORIZONTALLY



ADA APPROVED



DIMMERS:

Integrated Low Voltage LED Fixture – requires Electronic Low Voltage (ELV) dimmer.

Integrated 120v LED Fixture – C-L Dimmers recommended.

For more specific dimmer information, please contact: engineering@quozel.com.

WARRANTY:

Please refer to Quozel.com for complete warranty information.

Bulbs:

- Bulbs not included unless otherwise noted.
- Vintage Bulbs supplied are not necessarily the maximum wattage allowed.
- Products using LED and Halogen bulbs come with bulb(s) supplied in carton.
- Wattages stated are the maximum recommended; however, you may use lower wattages to suit your lighting needs.

LED:

- Integrated LED information chart provided wherever applicable.

Chain:

- (Single Tier) Chandelier, Dinette, Mini Chandeliers, Pendants, Mini Pendants and Island Lights come with 8' of wire and 4' of chain.
- (Two & Three Tier) Chandeliers and Foyer Fixtures come with 12' of wire and 8' of chain.
- All Outdoor Hanging Fixtures come with 12' of wire and 8' of chain.
- All Chain-Hung Mini Pendants come with 8' of wire and 4' of chain.

Other:

- All Rod-Hung Mini Pendants come with a minimum of 8' of wire.
- All Cord-Hung Mini Pendants come with a minimum of 8' of cord.
- All Cable-Hung Mini Pendants come with a minimum of 8' of cable.

Damp / Wet Locations:

- All flush and semi-flush mounted fixtures, bath fixtures and chandeliers are "Damp Location" listed.
- All outdoor hanging fixtures are "Damp Location" listed.
- All outdoor wall and post lights are "Wet Location" listed.

Electrical:

- All electrical fixtures are rated at 120-volt AC unless otherwise noted.
- Unless specified, all electrical fixtures are cUL or ETL listed.

Hardware:

- Backplate information and HCWO (Height from Center of Wall Opening) included for most wall fixtures (including outdoor) and bath fixtures.
- Canopy information included on almost all fixtures.
- All mirrors come with mounting hardware.

Tiffany / Naturals:

- Glass color in Tiffany lighting products vary in color. No two pieces are identical.
- Products that use natural materials are perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.

Glass / Shades:

- Will appear darker when not illuminated.

In our efforts to constantly improve our products, changes may be made throughout the year that vary from printed information in the catalog.

Contents

COLLECTIONS

Adonis	38	Kendra	64
Baroness	40	Kyle	68
Brook Hall	42	La Parra	74
Buchanan	44	Marquette	78
Downtown	46	Monterey Mosaic	81
Duchess	52	Taylor	87
Dury	58	Trilogy	92
Emery	61	Whitney	96

MINI-COLLECTIONS

Adams	102	Tavern	120
Alexandria	104	Palmer	122
Eastvale	105	Remi	123
Chamber	106	Odell	124
Armelle	108	Opera	126
Baron	110	Noble	128
Castile	111	Sophia	130
Milbank	112	New Harbor	133
Grant	114	Wilder	134
Laila	116	Tricia	136
Metropolis	117	Union Station	138
New England	118		

ADDITIONAL PRODUCTS & ACCESSORIES

Red number represents the category's appearance in our Photo Index immediately following this page.

Black number represents actual appearance in catalog.

Dining & Foyer and More	8, 141	Flush Mounts	23, 302
The Platinum Collection	10, 172	Track Lighting	24, 311
Designer Showcase:		Wall Fixtures	25, 317
Carolyn Kinder	12, 207	Bath Fixtures	26, 321
UPTOWN / Sergio Orozco	12, 216	Outdoor Fixtures	29, 371
Quoizel Naturals	13, 227	Tiffany	31, 459
Island Lights	15, 253	Table & Floor	33, 507
Pendants	16, 263	Mirrors	36, 527
Mini Pendants	18, 278	Accessories	534
Semi-Flush Mounts	20, 287	Full Product Index	538

Collections



Adonis (ADS) 38-39



Baroness (BNS) 40-41



Brook Hall (BKH) 42-43



Buchanan (BCN) 44-45



Downtown (DW) 46-51



Duchess (DH) 52-57



Dury (RDY) 58-60



Emery (ER) 61-63



Kendra (KD) 64-67



Kyle (KY) 68-73



La Parra (LP) 74-77



Marquette (MQ) 78-80



Monterey Mosaic (MY)
81-86



Taylor (TY) 87-91



Trilogy (TRG) 92-95



Whitney (WHI) 96-100

Mini-Collections

PHOTO INDEX



Adams (ADA) 102-103



Alexandria (AX) 104



Eastvale (EVE) 105



Chamber (CHB) 106-107



Armelle (AME) 108-109



Baron (BRO) 110



Castile (CS) 111



Milbank (MBK) 112-113



Grant (GRT) 114-115



Laila (LLA) 116



Metropolis (MTP) 117



New England (NA)
118-119



Tavern (TVN) 120-121



Palmer (PLR) 122



Remi (REM) 123



Odell (ODL) 124-125



Opera (OPA) 126-127



Noble (NBE) 128-129



Sophia (SPH) 130-132



New Harbor (NHR) 133



Wilder (WLR) 134-135



Tricia (TCA) 136-137



Union Station (UST)
138-140

Dining & Foyer



Auburn (ABN) 142-144



Mirren (MRN) 145



Castle Hill (CTH) 146-147



Voyager (VYR) 148-149



Carrabelle (CRE)
150-151



Wesley (WSY) 152-153



Estate (EST) 154



Dunn (DUN) 155



Woodrow (QF) 155



Silhouette (SLT) 156



Belhaven (BHN) 157



Alston (QMC) 158-159



Majesty (MJY) 159



Miramar (MMR) 159



Bandelier (BDR) 160



Wyndmoor (WDM) 160



Capri (CP) 160



Ridge Manor (QF) 161



Collins (QF) 161



Frontier (FTR) 161



Celestial (CLT) 162



Kemper (KPR) 162



Amelia (AML) 162



Serenity (SER) 163



Majestic (MJT) 164-165

PHOTO INDEX



Holbrook (HK) 166



Planter (QF) 166



Thornhill (THL) 167



Menlo (MNO) 167



Lakeside (LKE) 168



Colton (CTO) 168



Grand Court (GCT) 168



Sabrina (SRA) 169



Kayden (KDN) 169



Unison (UNS) 169



Pembroke (PB) 170



Burgess (BGS) 170



Anchor (ANR) 171



Knotting (QF) 171

Platinum Collection

PLATINUM
by QUOIZEL



Bordeaux (BRX) 174-177



Galaxy (PCGX) 178



Countess (PCCT) 179



Alexa (PCAX) 179



Crowne (PCCR) 180



Crystal Leaf (PCCF) 180



Arena (PCAN) 180



Mercury (PCMY) 181



Treasure (PCTS) 181



Shimmer (PCSR) 181



Vision (PCVN) 182



Paragon (PRN) 182



Highrise (PCHE) 183




Janelle (PCJL) 183



Ella (PCEL) 184



Superior (PCSP) 184



Valla (VLA) 185



Ribbons (RBN) 186-189



Abode (PCAE) 190-191



Array (PCAY) 190




Stellar (PCSL) 192



Encompass (PCEC) 192



Paragon (PRN) 193



Shimmer (PCSR) 194



Alexa (PCAX) 195

PHOTO INDEX



Endless (PCED) 195



Evermore (EME) 196-197



Pierre (PCPR) 198



Royale (RYE) 198



Seaview (PCSW) 199



Serena (PCSA) 200



Lacombe (PCLC) 201



Mirabella (PCMR) 201



Divine (PCDV) 202



Dash (PCDH) 203



Glacial (PCGL) 203



Valiant (PCVT) 204



Blade (PCBD) 204



Pace (PCPC) 205



Promenade (PCPE) 205



Bram (PCBM) 206

Carolyn Kinder



Confetti (CKCF) 208-209



Metro (CKMO)
210-211



Sanctuary (CKSC)
212



Brookmont (CKBT) 212



Hickman (CKHM) 212



Ultra (CKUT) 212



Marisol (CKMS) 213



Kendrick (CKKD) 215



Nikos (CKNK) 215



Gaston (CKGN) 215



Sonia (CKSN) 215

Uptown by Sergio Orozco




East Village (UPEV)
216-217



Theater Row (UPTR) 218



Ritz (UPRZ) 219



Carnegie (UPCN)
220-221



Madison Manor (UPMM)
222-223



Columbus Circle (UPCC)
224



Fulton (UPFT)
224



Penn Station (UPPS) 225



Seaport (UPSE) 226



Holita (UPHL) 226



Kendra (KD) 64-67



Kyle (KY) 68-73



Monterey Mosaic (MY)
81-86



Chamber (CH) 106-107



Armelle (AME) 108-109



Baron (BRO) 110



Castile (CS) 111



Tavern (TVN) 120-121



Odell (ODL) 124-125



Auburn (ABN) 142-144



Belhaven (BHN) 157



Wyndmoor (WDM) 160



Holbrook (HK) 166



Planter (QF) 166



Kayden (KDN) 169



Pembroke (PB) 170



Anchor (ANR) 171



Laguna (MCLG) 228-232



Prism (MC) 233



Alistar (MCAL) 233



San Gabriel (NX) 234



Cyrus (MCCS) 234



Kingsford (MCKD) 235



Morrow (MC) 235



Vega (MC) 236

Naturals



Pearce (PER) 236



Belfair (MCBF) 237



Highland (MC) 237



Bandelier (BDR) 238



Tartan (MC) 238



Whispering Wood
(AG) 238



Zen (ZE) 239



Arcadia (AI) 240



Zephyr (ZP) 240



Aristocrat (AS) 241



Pomez (TF) 242-243



Captiva (SSCV) 244



Floret (SSFT) 244



Sanibel (SSSB) 245



Flower Field (JD) 245




Kayden (KDN) 280



Alexandria (AX) 254



Brook Hall (BKH) 254



Laguna (MCLG) 254



Adonis (ADS) 255



Emery (ER) 255



Eastvale (EVE) 256



Tavern (TVN) 256-257



New Harbor (NHR) 256



Confetti (CKCF) 258



Marisol (CKMS) 258



Duchess (DH) 259



LaParra (LP) 259



Kyle (KY) 260



Deluxe (DX) 261



Taylor (TY) 261



Remi (REM) 261



Asheville (TFAS) 262



Belle Fleur (TFBF) 262



Inglenook (TFIK) 262

Pendants



Adonis (AD) 39



Baroness (BN) 41



Buchanan (BCN) 45



Downtown (DW) 51



Duchess (DH) 54



Dury (RDY) 60



Emery (ER) 62



Kendra (KD) 67



Kyle (KY) 72



Monterey Mosaic (MY) 84



Trilogy (TRG) 94



Adams (ADA) 103



Alexandria (AX) 104



Eastvale (EVE) 105



Milbank (MBK) 113



Grant (GRT) 115



Metropolis (MTP) 117



Palmer (PLR) 122



Odell (ODL) 125



Wilder (WLR) 134



Bordeaux (BRX) 174



Galaxy (PCGX) 178



Arena (PCAN) 180



Crystal Leaf (PCCF) 180



Mercury (PCMY) 181

PHOTO INDEX



Vision (PCVN) 182



Janelle (PCJL) 183



Superior (PCSP) 184



Valla (VLA) 185



Ribbons (RBN) 186-189



Abode (PCAE) 190



Encompass (PCEC) 192



Confetti (CKCF) 208-209



Metro (CKMO) 210



Marisol (CKMS) 213



Fulton (UPFT) 224



Penn Station (UPPS) 225



Laguna (MC) 228



Morrow (MC) 235



Kingsford (MCKD) 235



Belfair (MCBF) 237



Bandelier (BDR) 238



Zen (ZE) 239



Arcadia (AI) 240



Aristocrat (AS) 241



Orion (ON) 264



Jarvis (JV) 265



Amelia (AML) 265



Portland (PTD) 266-267



Brown Lattice (BWL) 267

Pendants



Capri (CP) 268



Bound (BND) 268



Railway (RLY) 268



Mirage (MIR) 269



Jolene (JLE) 269



Cody (CDY) 270



Morroco (QF) 270



Cloverdale (CRA) 271



Long Beach (LBH) 271



Tiffany- many styles available
See section starting on p.459

Mini-Pendants



Adonis (AD) 39



Baroness (BNS) 40



Downtown (DW) 51



Duchess (DH) 56



Dury (RDY) 60



Emery (ER) 62



Kendra (KD) 67



Kyle (KY) 73



La Parra (LP) 76



Monterey Mosaic (MY)
86

PHOTO INDEX



Trilogy (TRG) 94



Eastvale (EVE) 105



Grant (GRT) 115



Metropolis (MTP) 117



New England (NA) 119



Sophia (SPH) 132



Wilder (WLR) 135



Union Station (UST) 140



Treasure (PCTS) 181



Ribbons (RBN) 187-189



Confetti (CKCF) 209



Sonia (CKSN) 215



Gaston (CKGN) 215



Kendrick (CKKD) 215



Nikos (CKNK) 215



Penn Station (UPPS) 225



Laguna (MC) 232



Kingsford (MCKD) 235



Pomez (TF) 243



Morroco (QF) 279



Garrison (QPP) 279



Brown Lattice (BWL) 280



Cody (CDY) 280



Ferndale (FE) 280



Kayden (KDN) 280

Mini-Pendants



Steadman (SDN) 281



Marine (MRE) 281



Ridley (QPP) 281



Dublin (DBN) 282



Antero (QPP) 282



Valentina (QPP) 282



Railway (RLY) 283



Highgate (QPP) 283



Tiffany- many styles available
See section starting on p.459

Semi-Flush Mounts



Baroness (BNS) 41



Brook Hall (BKH) 42



Buchanan (BCN) 45



Downtown (DW) 51



Duchess (DH) 56



Dury (RDY) 60



Kendra (KD) 67



Kyle (KY) 72



Monterey Mosaic (MY) 85



Taylor (TY) 90

PHOTO INDEX



Trilogy (TRG) 95



Whitney (WHI) 100



Baron (BRO) 110



Castile (CS) 111



Milbank (MBK) 113



Metropolis (MTP) 117



Tavern (TVN) 120



Palmer (PLR) 122



New Harbor (NHR) 133



Wilder (WLR) 135



Union Station (UST) 140



Alexa (PCAX) 179



Crowne (PCCR) 180



Shimmer (PCSR) 181



Vision (PCVN) 182



Superior (PCSP) 184



Array (PCAY) 190



Abode (PCAE) 190



Confetti (CKCF) 209



Metro (CKMO) 210



Marisol (CKMS) 213



Theater Row (UPTR) 218



Penn Station (UPPS) 225



Laguna (MC) 228



Kingsford (MCKD) 235

Semi-Flush Mounts



Pearce (PER) 236



Belfair (MCBF) 237



Zen (ZE) 239



Arcadia (AI) 240



Aristocrat (AS) 241



Sanibel (SSSB) 245



Brown Lattice (BWL) 288



Burgess (BGS) 288



Frontier (FTR) 288



Norwood (QF) 289



Celestial (CLT) 289



Waverly (WV) 290



Cloverdale (CRA) 290



Deluxe (DX) 290-291



Sailor (SLR) 292



Calvary (QF) 292



Ashland (QF) 293



Ozark (OZ) 293



Griffin (GF) 294-295



Jolene (JLE) 296



Majesty (MJY) 296



Mirage (MIR) 296



Cody (CDY) 297



Warren (QF) 297



Belcourt (QF) 297



Castle (QF) 297

Tiffany - many styles available
See section starting on p.459



Flush Mounts

PHOTO INDEX



Adonis (ADS) 39




Monterey Mosaic (MY) 85



Chamber (CHB) 106



Laila (LLA) 116



Opera (OPA) 127



Bordeaux (BRX) 175-176



Countess (PCCT) 179



Paragon (PRN) 182



Highrise (PCHE) 183



Ella (PCEL) 184



Valla (VLA) 185



Ribbons (RBN) 187, 189



Laguna (MCLG) 229



Zen (ZE) 239



Melon (ML) 302



Manor (MNR) 303



Summit (SMT) 304



Griffin (GF) 305



Ozark (OZ) 306



Wilson (WLS) 307



Bound (BND) 307



**Tiffany - many styles available
See section starting on p.459**

Track Lighting



Duchess (DH) 312



Kyle (KY) 312



Monterey Mosaic (MY) 312



Pacifica (PF) 313



Denning (QTR) 313



Eastvale (EVE) 313



Asheville (TFAS) 315



Inglenook (TFIK) 315



Victory (TFVY) 315



Taylor (TY) 316

Wall Lighting

PHOTO INDEX



Adonis (ADS) 38



Downtown (DW) 49



Duchess (DH) 57



Kendra (KD) 65



Kyle (KY) 73



La Parra (LP) 76



Marquette (MQ) 79



Monterrey Mosaic (MY) 86



Taylor (TY) 91



Trilogy (TRG) 95



Whitney (WHI) 97



Adams (ADA) 103



Armelle (AME) 109



Remi (REM) 123



Noble (NBE) 129



Tricia (TCA) 137



Uptown East Village (UPEV) 217



Uptown Theater Row (UPTR) 218



Uptown Madison Manor (UPMM) 222



Uptown Seaport (UPSE) 226



Uptown Holita (UPHL) 226



Millenium (LSM) 318



Yuma (YU) 318



Tiffany - many styles available
See section starting on p. 459



Bath - many styles available
See section starting on p. 321

Bath Lighting



Bram (PCBM) 322



Pierre (PCPR) 323



Endless (PCED) 323



Valiant (PCVT) 324



Blade (PCBD) 324



Pace (PCPC) 325



Promenade (PCPE) 325



Dash (PCDH) 326



Glacial (PCGL) 326



Alexa (PCAX) 327



Shimmer (PCSR) 328



Seaview (PCSW) 329



Serena (PCSA) 330



Lacombe (PCLC) 331



Mirabella (PCMR) 331



Divine (PCDV) 332



Devlin (DVN) 333



Downtown (DW) 334-335



Erin (ERN) 336



Tatum (TU) 337




Quinton (QI) 338



Nolan (NN) 339



Kolt (KLT) 340-341



Adano (AN) 342



Broadgate (BGT) 343



Bower (BWR) 344



Dublin (DBN) 345



Duchess (DH) 346-347



Hollister (HS) 348



Deluxe (DX) 349



Edison (EDS) 350



Garrison (GRN) 351



Demitri (DI) 352-354



Loft (LFT) 355



Melody (MLD) 356




Menlo (MNO) 357

Bath Lighting



Pacifica (PF) 358-359



Nicholas (NL) 360



North Gate (NGT) 361



Parallel (PRL) 362



Supreme (SPR) 363



Tritan (TT) 364



Tranquil Bay (TB) 365



Taylor (TY) 366-367



Paragon (PRN) 368



Evermore (EME) 369



Royale (RYE) 370

Outdoor Lighting

PHOTO INDEX



New England (NA) 119



Zephyr (ZP) 240



Monument (MNT) 372



Newbury (NY) 373-379



Alto (ALT) 380



Ryland (RYD) 380



Cole (COE) 381



Stonington (SNN)
382-385



Cathedral (CAT)
386-389



Fort Quinn (FQ) 390-393



Bedford (BFD) 394-395



Tudor (TDR) 396-397



Marblehead (MBH)
398-400



Crestview (CVW) 401



Miles (MLS) 402-403



Booker (BKR) 404-405



Hunter (HTR) 406-407



Oasis (OAS) 408-409



Harmony (HY) 410-411



Hillcrest (HC/HCE)
412-415



Lodge (LDG) 416-417



Millhouse (MHE)
418-419



Rue de Royal (RO)
420-421



Chalmers (CM) 422-423



Cooper (COR) 424-425

Outdoor Lighting



Marine (MRE) 426-427



Devon (DE) 428-429



Ridge (RGE) 430-431



Rutledge (RJ) 432-433



Byron (BRN) 434-435



Steadman (SDN) 436-437



Galen (GLN) 438-440



Chancellor (CCR) 441



Trumbull (TML) 442-443



Province (PRV) 444-445



Powell (PWL) 446-447



Bain (BAN) 448-450



Seaford (SFD) 451



Grover (GVR) 452-453



Georgetown (GT) 454-455



Chimera (CHI) 456-457



Milan (MLN) 458



Victory (TFVY)
460-461



Alcott (TFAT)
462-463



Inglenook (TFIK)
464-468



Carroll 469



Asheville (TFAS) 470-474



Larissa 475



Kami (TFKM) 476-478



Stephen (TFST) 479-481



Monteclair (TFMC) 482



Belle Fleur (TFBF) 483



West End 484-485



Pomeroy 486



Gotham 486



Hyacinth 487



Pueblo 488, 489



Montgomery 488



Jewel Dragonfly (TFJD) 490



King 491




Copperfly 491



Arden 492



Revere 492



Orange Butterfly 493



Green Frog 493



Flowered Ladybug 493



Lounging Frog 493



Angel Fish 493



Rainbow Butterfly 493



Flower Turtle
493



Purple Wisteria 494



Laburnum 494



Lynch 494



Mariah 495



Jewel 495



Berkshire 495



Alahambre 496



Graham 496



Grove Park 497



Indus 497



Lucia 498



Queens Meadow 498



Reed 496



Connie 498



Adriana 499



Florentine 499



Lance 500



Pearson 500



Ava 501



Chastain 501



Bryant 502



Holmes 502



Bragg Creek 503



Navajo 503



Gibbons 503



Palmetto 504



Fields 504



Cambridge 504



India 505



Viking 505



Jewel Heart 505



Lennon 506



Kelso 506



Classic Craftsman 506

Table&Floor



Kyle (KY) 73



Union Station (UST) 140



Confetti (CKCF) 208



Brookmont (CKBT) 212



Hickman (CKHM) 212



Laguna (MCLG) 229



Alistar(MC) 233



Prism (MC) 233



Cyrus (MCCS) 234



San Gabriel 234

Table&Floor



Pearce (PER) 236



Vega (MC) 236



Highland (MC) 237



Tartan (MC) 238



Whispering Wood (AG)
238



Pomez 243



Captiva (SSCV) 244



Floret (SSFT) 244



Sanibel (SSSB) 245



Flower Field (JD) 245



Kingsley (VVKY) 508-509



Benedict (VVB T) 510



Cruise (VVCS) 510



Ambrose (VVAM) 511



Whitney (VVWH) 511



Spencer (VVSP) 512



Thompson (VVTH) 512



Buckler 513



Stockton 514-515



Archer 515



Humphrey 516



Innovation 516



Jensen 516



Haskell 517



Lyndhurst 517



Weaving 517

PHOTO INDEX



Jenkins 517



Bray 517



Marx 518



Sway 518



Encore 518



Westway 519



Studio 519



Blaine 519



Ocean 520



Slade 520



Blue River 520



Dune 520



Looping 521



Sable 521



Starling 521



Percy 521



Aquatic 521



Barrel 522



Seaside 522



Abbey 522



Sandy 522



Garnet 523



Satin Lace 523



Abigail Adams 523



Linear 524



Beckett 524

Table&Floor



Glenhaven 524




String Shade 524



Tiffany - many styles available
See section starting on p. 459

Mirror



Woodmere 528



Carrigan 528



Hearst 528




Vanderbilt 528



Finn 529



Sage 529



Tallon 529



Soho 529



Duchess 530



Greystone 530



Jasper 530



Taylor 530



Gwyneth 531



Monterey Mosaic 531



Maxim 531



Shelburne 531



Downtown 532



Norton 532



Ritz 532



Envision 532



Breckenridge 533



Marcos 533



Vista 533



Confetti 533



Ultra 533

At Quoizel, we constantly strive to ensure that the metal and glass finishes shown in the catalog match our actual products. However, variations in printing and chemical finishes may cause some differences between the printed images and actual product.

Collections | QUOIZEL



Whether your décor is traditional, contemporary, or somewhere in the middle, Quoizel presents a diverse offering of coordinated lighting fixtures which will complement and enhance your home.

Browse the pages which follow and find that unique **Quoizel Collection** which fits your own personal style!

From the **DURY COLLECTION** (page 58)
Hanging Fixture: **RDY5208PN**

Adonis COLLECTION

FINISH:

Dark c herry

GLASS:

o pal etched and c lear Water

DAMP ADS8701DC



DAMP ADS5005DC





ADS639DC DAMP



DAMP ADS1504DC



DAMP ADS1615DC



DAMP ADS2818DC

Adonis COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
ADS1504DC	7.5" H*, 4.5" W, 4.5" Dp.	6"	-	1-100W Med. Base or 23W CFL
ADS1615DC	9" H, 15" W, 15" Dp.	-	-	2-60W Med. Base or 13W CFL
ADS2818DC	28" H, 18" W, 18" Dp.	6"	-	3-100W Med. Base or 23W CFL
ADS5005DC	22" H, 26" W, 26" Dp.	6"	-	5-60W Cand. Base
ADS639DC	19"H**, 39" W, 19.5" Dp.	8" x 4.5"	-	6-60W Cand. Base
ADS8701DC	14" H, 5.5" W, 7" Ext.	5.5" x 5.5"	9.75"	1-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire.
 *Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods

Baroness COLLECTION

FINISH:
Western Bronze

SHADE:
Wire

DAMP BNS1505WT

NEW!

FOR ♦ 2016

DAMP BNS5009WT

VINTAGE STYLE
bulb included





BNS5005WT DAMP



DAMP **BNS2818WT**


NEW!
FOR ♦ 2016



DAMP **BNS1715WT**



BNS5204WT DAMP



Baroness COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
BNS1505WT	8.5" H*, 5" W, 5" Dp.	1.25" x 5"	1-60W Vintage Bulb Supplied**
BNS1715WT	15.5" H, 15.5" W, 15.5" Dp.	1.5" x 5.5"	3-60W Vintage Bulb Supplied**
BNS2818WT	27.5" H, 18" W, 18" Dp.	5"	4-60W Vintage Bulb Supplied**
BNS5005WT	24" H, 25" W, 25" Dp.	5"	5-60W Vintage Bulb Supplied**
BNS5009WT†	33" H, 33" W, 33" Dp.	5"	9-60W Vintage Bulb Supplied**
BNS5204WT†	31" H, 15" W, 15" Dp.	5"	4-60W Vintage Bulb Supplied**

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. †Fixture comes with 12' of wire and 8' of chain. *Comes with (2) 12" and (2) 6" Rods. **Max Wattage: 100W Med. Base or 23W CFL

Brook Hall COLLECTION

FINISH:
Western Bronze

BKH1714WT



NEW!
FOR ♦ 2016

BKH838WT



PAINTED
BRASS
ACCENTS



BKH5208WT DAMP



DAMP **BKH5204WT**

NEW!
FOR ♦ 2016



DAMP **BKH5303WT**

Brook Hall COLLECTION

PRODUCT	DIMENSIONS	CANOPIY	BULBS
BKH1714WT	14" H, 14" W, 14" Dp.	6"	3-100W Med. Base or 23W CFL
BKH5204WT†	28.5" H, 13" W, 13" Dp.	5"	4-60W Cand. Base
BKH5208WT†	43" H, 18" W, 18" Dp.	5" x 5"	8-60W Cand. Base
BKH5303WT	25" H, 10" W, 10" Dp.	5"	3-60W Cand. Base
BKH838WT	15.5" H, 38" W, 12" Dp.	9" x 4.75"	8-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. †Fixture comes with 12' of wire and 8' of chain.

Buchanan COLLECTION

FINISH:

Western Bronze

GLASS:

clear Seedy

BCN5009WT DAMP

NEW!

FOR ♦ 2016





BCN5006WT DAMP



DAMP **BCN2820WT**

DAMP **BCN5204WT**



NEW!
FOR ♦ 2016



DAMP **BCN1716WT**

Buchanan COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BCN1716WT	14.5" H, 16" W, 16" Dp.	1" x 6"	3-100W Med. Base or 23W CFL
BCN2820WT	25.5" H, 20" W, 20" Dp.	.75" x 5"	4-100W Med. Base or 23W CFL
BCN5006WT	20" H, 25" W, 25" Dp.	1" x 6"	6-60W Cand. Base
BCN5009WT†	30" H, 33" W, 33" Dp.	1" x 6"	9-60W Cand. Base
BCN5204WT†	26.5" H, 14.5" W, 14.5" Dp.	1" x 6"	4-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. †Fixture comes with 12' of wire and 8' of chain.

Downtown COLLECTION

FINISH:

C Polished chrome **D** Dusk Bronze **NEW!**

GLASS:

opal etched

DW5015D   

NEW!

FOR ♦ 2016



Downtown COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DW5015C/D	41.5" H, 44" W, 44" Dp.	6"	15-100W Med. Base or 23W CFL

Chain-hung fixture comes with 12" of wire and 8' of chain.



From the **DOWNTOWN COLLECTION:**
DW5005C
Photo courtesy of Innovative Custom Homes

Downtown COLLECTION

FINISH:

C Polished chrome **D** Dusk Bronze **NEW!** **BN** Brushed nickel **NEW!**

GLASS:

opal etched

DAMP **50** **DW5009C**



DAMP **DW5005D**

NEW!

FOR ♦ 2016



DW5004C **DAMP**



Downtown COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DW5004C/D	19.5" H, 22" W, 22" Dp.	6"	4-100W Med. Base or 23W CFL
DW5005C/D	26" H, 28" W, 28" Dp.	6"	5-100W Med. Base or 23W CFL
DW5009C/D†	33" H, 36" W, 36" Dp.	6"	9-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. †Fixture comes with 12' of wire and 8' of chain.



DW43222BN

MOUNTS

NEW!

FOR 2016



DW8701BN

DW8602CLED



DW8603BNLED



MOUNTS

NEW!

FOR 2016

DW8604BNLED



Downtown COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DW43222BN	32" H, 22" W, 1.5" Dp.	-	-	-
DW8602BNLED/CLED	7.5" H, 15" W, 7" Ext.	8" x 5"	5"	2-4.5W Frosted G9 LED Dimmable Bulb Supplied
DW8603BNLED/CLED	7.5" H, 24.5" W, 7" Ext.	8" x 5"	5"	3-4.5W Frosted G9 LED Dimmable Bulb Supplied
DW8604BNLED/CLED	7.5" H, 33.5" W, 7" Ext.	8" x 5"	5"	4-4.5W Frosted G9 LED Dimmable Bulb Supplied
DW8701BN/C	10.5" H, 6" W, 8" Ext.	8" x 5"	7.75"	1-100W Med. Base or 23W CFL

Downtown bath fixtures can be mounted as uplights or downlights. DW43222BN can be mounted vertically or horizontally.



From the **DOWNTOWN COLLECTION:**
DW2817C
Photo courtesy of Phil Kean Design Group

Downtown COLLECTION

FINISH:

C Polished chrome **D** Dusk Bronze **NEW!**

GLASS:

opal etched



DW2817C  



 **DW1506D**

NEW!
FOR ♦ 2016

DW1824D  



DW1717C  



Downtown COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.	SHADE
DW1506C/D	12.5" H*, 6" W, 6" Dp.	5.5"	1-100W Med. Base or 23W CFL	-	
DW1717C/D	13.5" H, 17" W, 17" Dp.	8"	3-100W Med. Base or 23W CFL	17" x 5.5"	Cream Linen
DW1824C/D	33" H, 24" W, 24" Dp.	6"	4-100W Med. Base or 23W CFL	24" x 8"	Cream Linen
DW2817C/D	24" H, 17" W, 17" Dp.	6"	3-75W Med. Base or 18W CFL	17" x 7.5"	Cream Linen

Chain-hung fixtures come with 8' of wire and 4' of chain.

*Comes with (2) 6" and (2) 12" Rods. Rod-hung fixtures come with 8' of wire.

Duchess COLLECTION

FINISH:

AN Antique Nickel

PN Palladian Bronze

GLASS:

AN Grey Marble

PN Champagne Marble

DH5009AN DAMP





DH5018AN DAMP 50 W



DH5105PN DAMP



DH5005PN DAMP

Duchess COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH5005AN/PN*	22.5" H, 24.5" W, 24.5" Dp.	6.5"	5-100W Med. Base or 23W CFL
DH5009AN/PN**	31" H, 31" W, 31" Dp.	6.5"	9-100W Med. Base or 23W CFL
DH5018AN/PN**	39" W, 41" H, 41" Dp.	6.5"	18-100W Med. Base or 23W CFL
DH5105AN/PN*	21" H, 24.5" W, 24.5" Dp.	6.5"	5-100W Med. Base or 23W CFL

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.

Duchess COLLECTION

FINISH:

AN Antique nickel

PN Palladian Bronze

GLASS:

AN Grey Marble

PN champagne Marble

DAMP DH5103AN



DAMP DH2820AN



DAMP DH348PN



Duchess COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH2820AN/PN	24" H, 20" W, 20" Dp.	6.5"	4-100W Med. Base or 23W CFL
DH348AN/PN	27" H, 48" W, 14" Dp.	6.5"	3-100W Med. Base or 23W CFL
DH5103AN/PN	20" H, 23" W, 23" Dp.	6"	3-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.



Duchess COLLECTION

FINISH:

AN Antique nickel

PN Palladian Bronze

GLASS:

AN Grey Marble

PN champagne Marble

DAMP DH1506PN

Enlarged for detail



DAMP DH1718PN



DAMP DH1404AN



All Quoizel Track Lights Swivel



DH8601AN DAMP



DH8602PN DAMP

MOUNTS

DAMP DH8603AN



DH44030PN

MOUNTS



DH8604PN DAMP

Duchess COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
DH1404AN/PN	12.5" H, 36.5" W, 6" Dp.	4.5"	-	4-100W Med. Base or 23W CFL	-
DH1506AN/PN	11" H*, 6" W, 6" Dp.	5.5"	-	1-100W Med. Base or 23W CFL	-
DH1718AN/PN	11" H, 17" W, 17" Dp.	5.5"	-	3-100W Med. Base or 23W CFL	-
DH43024PN**	30" H, 24" W, 1.5" Dp.	-	-	-	Beveled
DH44030PN	40" H, 30" W, 1.5" Dp.	-	-	-	Beveled
DH8601AN/PN	11" H, 6" W, 8" Ext.	4.75" x 6.75"	7.5"	1-100W Med. Base or 23W CFL	-
DH8602AN/PN	11" H, 16" W, 7.5" Ext.	9" x 5"	7.5"	2-100W Med. Base or 23W CFL	-
DH8603AN/PN	11" H, 23" W, 7.5" Ext.	9" x 5"	7.5"	3-100W Med. Base or 23W CFL	-
DH8604AN/PN	11" H, 31.5" W, 7.5" Ext.	9 x 5	7.5"	4-100W Med. Base or 23W CFL	-

**Not Shown. *Comes with (2) 6" and (2) 12" Rods. Duchess bath fixtures can be mounted as uplights or downlights. All rod-hung fixtures come with 8' of wire. Mirrors may be hung vertically or horizontally.

Dury COLLECTION

FINISH:

CS century Silver Leaf

PN Palladian Bronze

RDY5208CS



Dury COLLECTION

PRODUCT

RDY5208CS/PN**

DIMENSIONS

36" H, 24.5" W, 24.5" Dp.

CANOPY

1" x 5.5"

BULBS

8-60W Cand. Base

Chain-hung fixture comes with 12' of wire and 8' of chain.




Dury COLLECTION

FINISH:

CS Century Silver Leaf

PN Palladian Bronze

VINTAGE STYLE
bulb included



DAMP RDY1506CS

DAMP RDY2823PN



DAMP RDY1714PN

*FAUX
MELTED WAX
CANDLES*



DAMP RDY2821CS

Dury COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RDY1506CS*	11" H, 6.5" W, 6.5" Dp.	5"	1-60W Vintage Bulb (Supplied)†
RDY1714CS/PN	14.5" H, 14.5" W, 14.5" Dp.	.75" x 5.5"	3-60W Cand. Base
RDY2821CS/PN	15" H, 21" W, 21" Dp.	5"	4-60W Cand. Base
RDY2823CS/PN	20" H, 23" W, 23" Dp.	1" x 5.5"	4-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. †Max wattage: 100W Med. Base or 23W CFL.

Emery COLLECTION

collection S

FINISH:

BN Brushed nickel **IS** imperial Silver **PN** Palladian Bronze

SHADE: Metal

Available in Three Finishes!

ER5103IS



ER5103PN



DAMP ER5103BN



Emery COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ER5103BN/IS/PN	15" H*, 24" W, 24" Dp.	5"	3-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Emery COLLECTION

FINISH:

BN Brushed nickel

IS imperial Silver

PN Palladian Bronze

SHADE: Metal

ER353PN  



ER1508IS 

Pendant converts to Semi-Flush Mount



(all finishes)

  **ER1814BN**



Emery COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ER1508BN/IS/PN	9" H*, 8" W, 8" Dp.	5"	1-100W Med. Base or 23W CFL
ER1814BN/IS/PN	11.5" H*, 13.5" W, 13.5" Dp.	5"	1-100W Med. Base or 23W CFL
ER353BN/IS/PN	23.5" H**, 52.5" W, 13" Dp.	9" x 4.5"	3-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods.



From the **EMERY COLLECTION:**
ER1814IS

Photo courtesy of Letitia Little Interior Design

Kendra COLLECTION

FINISH:
Mottled Silver

SHADE:
oyster Mica

ELONGATED
CRYSTAL
DROPS

50 100W DAMP KD5015MM

QUOIZEL
NATURALS
MICA





KD5009MM DAMP

QUOIZEL
NATURALS
MICA



DAMP **KD5005MM**



KD8701MM DAMP

Kendra COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
KD5005MM*	31" H, 27" W, 27" Dp.	5.5"	-	5-60W Cand. Base
KD5009MM**	39" H, 34" W, 34" Dp.	5.5"	-	9-60W Cand. Base
KD5015MM**	53" H, 44" W, 44" Dp.	5.5"	-	15-60W Cand. Base
KD8701MM	13.5" H, 6" W, 10" Dp.	4.5" x 6.5"	6.25"	1-60W Cand. Base

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.
Due to natural properties, shade color may vary.



From the **KENDRA COLLECTION:**
KD5009MM

Kendra COLLECTION

collections

FINISH:
Mottled Silver

SHADE:
oyster Mica

 **KD1507MM**

QUOIZEL
NATURALS
MICA

 **KD2824MM**



KD2816MM 



 **KD1716MM**



Kendra COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
KD1507MM	12" H*, 7" W, 7" Dp.	5.5"	1-100W Med. Base or 23W CFL
KD1716MM	12.5" H, 16" W, 16" Dp.	5.5"	3-60W Med. Base or 13W CFL
KD2816MM	22" H, 17" W, 17" Dp.	5.5"	2-100W Med. Base or 23W CFL
KD2824MM	29" H, 24" W, 24" Dp.	5.5"	4-60W Med. Base or 13W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.
Rod-hung fixture comes with 8' of wire. * Comes with (2) 6" and (2) 12" Rods.
Due to natural properties, shade color may vary.

Kyle COLLECTION

FINISH:

- IB** imperial Bronze
- IN** iron Gate

SHADE:

- IB** Butterscotch o nyx
- IN** White o nyx

QUOIZEL
NATURALS
ONYX

50   **KY5016IB**



Kyle COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
KY5016IB	48" H, 42" W, 42" Dp.	7"	16-100W Med. Base or 23W CFL

Chain-hung fixture comes with 12' of wire and 8' of chain.



From the **KYLE COLLECTION:**
Hanging Fixture: **KY2822IB** Mini Pendant: **KY1507IB**
Photo courtesy of Devane Design

Kyle COLLECTION

FINISH:

IB imperial Bronze

IN iron Gate

SHADE:

IB Butterscotch o nyx

IN White o nyx

   **KY5009IN**



 **KY5106IB**



KY5006IN  



QUOIZEL
NATURALS
ONYX


DAMP KY5103IN

Enlarged for detail



Quoizel artisans take the natural beauty of onyx and create unique solutions for home lighting.

DAMP KY433IB



KY540IN DAMP



QUOIZEL
NATURALS
ONYX

Kyle COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
KY433IB*	18.5" H, 33" W, 4.5" Dp.	8" x 4.5"	4-100W Med. Base or 23W CFL
KY5006IB/IN*	28" H, 28" W, 28" Dp.	5.5"	6-100W Med. Base or 23W CFL
KY5009IB/IN**	34.5" H, 35" W, 35" Dp.	5.5"	9-100W Med. Base or 23W CFL
KY5103IB/IN*	22" H, 20" W, 20" Dp.	5.5"	3-100W Med. Base or 23W CFL
KY5106IB*	24" H, 24" W, 24" Dp.	1.25" x 5.5"	6-100W Med. Base or 23W CFL
KY540IB/IN*	23" H, 40" W, 5.5" Dp.	11.75" x 4.75"	5-100W Med. Base or 23W CFL

*Chain-hung fixtures come with 8' of wire and 4' of chain.

**Chain-hung fixture comes with 12' of wire and 8' of chain. Due to natural properties, shade color may vary.

Kyle COLLECTION

FINISH:

IB imperial Bronze

IN iron Gate

SHADE:

IB Butterscotch o nyx

IN White o nyx

DAMP KY5506IB



DAMP KY5503IB



DAMP KY2822IB



KY1716IB **DAMP**



KY1404IB **DAMP**



All Quoizel Track Lights Swivel

QUOIZEL
NATURALS
ONYX



KY8801IN DAMP

Enlarged for detail



DAMP **KY1507IB**



DAMP **KY1508IN**



KY6328IB

QUOIZEL
NATURALS
ONYX



DAMP **KY8701IN**

Kyle COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
KY1404IB	14.5" H, 36" W, 4.5" Dp.	8.25" x 4.5"	-	4-100W Med. Base or 23W CFL
KY1507IB/IN	20" H*, 8" W, 8" Dp.	5"	-	1-100W Med. Base or 23W CFL
KY1508IB/IN	7" H*, 5" W, 5" Dp.	5"	-	1-100W Med. Base or 23W CFL
KY1716IB	11" H, 16" W, 16" Dp.	5"	-	3-100W Med. Base or 23W CFL
KY2822IB	22.5" H, 24" W, 24" Dp.	5.5"	-	5-75W Med. Base or 18W CFL
KY5503IB	19.5" H, 17" W, 17" Dp.	5.5"	-	3-100W Med. Base or 23W CFL
KY5506IB	23" H, 23" W, 23" Dp.	5.5"	-	6-100W Med. Base or 23W CFL
KY6328IB	30" H, 14" W, 14" Dp.	-	-	2-100W Med. Base or 23W CFL
KY8701IB/IN	16" H, 4.5" W, 5.5" Ext.	4.5" x 8.25"	-	1-100W Med. Base or 23W CFL
KY8801IB/IN	11" H, 8.5" W, 4.5" Ext.	4.75" x 4.75"	5.5"	1-75W Med. Base or 18W CFL + 1-7W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Comes with (2) 6" and (2) 12" Rods. Rod-hung fixtures come with 8' of wire. Due to natural properties, shade color may vary.

La Parra COLLECTION

FINISH:
imperial Bronze

GLASS:
Candella Scavo

LP5018IB   





LP5009IB **DAMP** **50**

CANDELLA
SCAVO
GLASS



DAMP LP5006IB

La Parra COLLECTION

PRODUCT	DIMENSIONS	CANOPIY	BULBS
LP5006IB*	30" H, 28" W, 28" Dp.	9"	6-100W Med. Base or 23W CFL
LP5009IB**	37" H, 30" W, 30" Dp.	9"	9-100W Med. Base or 23W CFL
LP5018IB**	56" H, 47.5" W, 47.5" Dp.	9"	18-100W Med. Base or 23W CFL

*Chain-hung fixture comes with 8' of wire and 4' of chain.

**Chain-hung fixtures come with 12' of wire and 8' of chain.

La Parra COLLECTION

FINISH:
imperial Bronze

GLASS:
Candella Scavo



DAMP LP8601IB

Enlarged for detail



DAMP LP639IB

DAMP LP1505IB



La Parra COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
LP1505IB	14.5" H, 5" W, 5" Dp.	5.25"	-	1-100W Med. Base or 23W CFL
LP639IB	46" H, 38" W, 19" Dp.	7" x 4.5"	-	6-100W Med. Base or 23W CFL
LP8601IB	9" H, 5" W, 7" Ext.	5" x 8"	4.8"	1-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.



Marquette COLLECTION

FINISH:
Heirloom

MQ5020HL   



CRYSTAL
DROPS



MQ5009HL DAMP



MQ8701HL DAMP



DAMP MQ5006HL

Marquette COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MQ5006HL*	38" H, 28" W, 28" Dp.	7"	-	6-60W Cand. Base
MQ5009HL**	41" H, 32" W, 32" Dp.	7"	-	9-60W Cand. Base
MQ5020HL**	60" H, 50" W, 50" Dp.	9"	-	20-60W Cand. Base
MQ8701HL	21.5" H, 8.5" W, 7.5" Dp.	6" x 6"	13.75"	1-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain.

**Chain-hung fixtures come with 12' of wire and 8' of chain.

Marquette COLLECTION

FINISH:
Heirloom



MQ5206HL DAMP

DAMP **MQ5208HL**



DAMP **MQ5003HL**



Marquette COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MQ5003HL*	24" H, 17" W, 17" Dp.	7"	3-60W Cand. Base
MQ5206HL**	41.5" H, 20.5" W, 20.5" Dp.	7"	6-60W Cand. Base
MQ5208HL**	55" H, 27" W, 27" Dp.	7"	8-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.

MontereyMosaic COLLECTION

FINISH:

Malaga

SHADE:

Pen Shell Mosaic

QUOIZEL
NATURALS
PEN SHELL

MY5005ML DAMP



MontereyMosaic COLLECTION

PRODUCT

MY5005ML

DIMENSIONS

28.5" H, 25" W, 25" Dp.

CANOPY

5"

BULBS

5-100W Med. Base or 23W

Chain-hung fixture comes with 8' of wire and 4' of chain. Due to natural properties, shade color may vary.



QUOIZEL
NATURALS
PEN SHELL



Quoizel artisans take the natural beauty of pen shell and bring the wonder of the ocean to your home décor.



From the **MONTEREY MOSAIC COLLECTION:**

Mirror: **MY430241ML** Wall Sconce: **MY8801ML** Dinette Fixture: **MY5103ML**

The Monterey Mosaic Collection is made with Pen Shell and is perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.

MontereyMosaic COLLECTION

FINISH:

Malaga

SHADE:

Pen Shell Mosaic

DAMP MY5103ML



MY2824ML DAMP



DAMP MY2816ML



QUOIZEL
NATURALS
PEN SHELL



MY1618ML DAMP



MY1613ML DAMP

QUOIZEL
NATURALS
PEN SHELL



MY1723ML DAMP

DAMP MY1718ML



MY1404ML DAMP

All Quoizel Track Lights Swivel

Monterey Mosaic COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MY1404ML	16.5" H, 43.5" W, 5" Dp.	7.25"	4-100W Med. Base or 23W CFL
MY1613ML	7" H, 16" W, 16" Dp.	11"	3-60W Med. Base or 13W CFL
MY1618ML	7" H, 18" W, 18" Dp.	.75" x 12"	4-60W Med. Base or 13W CFL
MY1718ML	13" H, 18" W, 18" Dp.	2" x 6"	4-100W Med. Base or 23W CFL
MY1723ML	14" H, 24" W, 24" Dp.	2" x 6"	5-100W Med. Base or 23W CFL
MY2816ML	22" H, 18" W, 18" Dp.	5"	3-100W Med. Base or 23W CFL
MY2824ML	28" H, 23.5" W, 23.5" Dp.	5"	4-100W Med. Base or 23W CFL
MY5103ML	24" H, 24" W, 24" Dp.	5"	3-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.
Due to natural properties, shade color may vary.

MontereyMosaic COLLECTION

FINISH:

Malaga

SHADE:

Pen Shell Mosaic

DAMP MY1506ML



MY430241ML

QUOIZEL
NATURALS
PEN SHELL



MY430242ML



DAMP MY8801ML

Enlarged for detail



MontereyMosaic COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MY1506ML	18" H*, 6" W, 6" Dp.	5"	-	1-100W Med. Base or 23W CFL
MY430241ML	30" H, 24" W, 1.5" Dp.	-	-	-
MY430242ML	30" H, 24" W, 1.5" Dp	-	-	-
MY8801ML	12" H, 9" W, 5" Ext	7" x 4.5"	4.75	2-60W Cand. Base

*Comes with (2) 6" and (2) 12" Rods. Due to natural properties, shade color may vary.

Taylor COLLECTION

COLLECTiONS

FINISH:
Antique Nickel

GLASS:
Opal Etched

DAMP TY8501AN

DAMP TY5005AN



Taylor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TY5005AN	20" H*, 25" W, 25" Dp.	5.5" x .875"	-	5-100W Med. Base or 23W CFL
TY8501AN	19.5" H, 5.5" W, 5" Ext..	5.5" x .875"	10"	1-100W Med. Base or 23W CFL

*Comes with (2) 12" and (2) 6" Rods. Rod-hung fixtures come with 8' of wire.





From the **TAYLOR COLLECTION**
Mirror: **TY43625AN** Wall Fixture: **TY8501AN** Chandelier: **TY5005AN**

Taylor COLLECTION

FINISH:

AN Antique nickel

BN Brushed nickel **NEW!**

WT Western Bronze

C Polished Chrome

GLASS: opal etched

DAMP TY628AN



DAMP TY1721AN



TY1716AN **DAMP**



TY1444WT **DAMP**

NEW!
FOR ♦ 2016

All Quoizel Track Lights Swivel

DAMP TY1404AN





TY43625AN

Taylor bath fixtures are also available in Antique Nickel, Brushed Nickel and Western Bronze finishes.



NEW!
FOR ♦ 2016

TY8601C

Enlarged for detail



TY8602C

DAMP



TY8603C

DAMP

MOUNTS



TY8604C

DAMP

Taylor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
TY1404AN	8.5" H, 43" W, 3" Dp.	.875" x 9"	-	4-60W Frosted G9 Halogen†	-
TY1444AN/WT	11" H, 44" W, 5" Dp.	9" x 4.75"	-	4-100W Med. Base or 23W CFL	-
TY1716AN	11.5" H, 16.5" W, 16.5" Dp.	5.5" x .875"	-	3-100W Med. Base or 23W CFL	Etched Painted White Inside
TY1721AN	13.5" H, 21" W, 21" Dp.	5.5" x .875"	-	4-100W Med. Base or 23W CFL	Etched Painted White Inside
TY43625AN	35.5" H, 25.5" W, 2" Dp.	-	-	-	Beveled
TY628AN	16.5" H*, 28" W, 16" Dp.	.875" x 9"	-	6-100W Med. Base or 23W CFL	-
TY8601AN/BN/C	7.5" H, 4.5" W, 5.5" Ext.	4.5" x 5"	5"	1-100W Med. Base or 23W CFL	-
TY8602AN/BN/C/WT	7.5" H, 13.5" W, 5.5" Ext.	7" x 4.5"	5.5"	2-100W Med. Base or 23W CFL	-
TY8603AN/BN/C/WT	7.5" H, 21" W, 5.5" Ext.	7" x 4.5"	5.5"	3-100W Med. Base or 23W CFL	-
TY8604AN/BN/C/WT	7.5" H, 30" W, 5.5" Ext.	7" x 4.5"	5.5"	4-100W Med. Base or 23W CFL	-

Rod-hung fixtures come with 8' of wire. *Comes with (4) 6" and (4) 12" Rods. †Bulbs Supplied.
Taylor bath fixtures may be mounted as uplights or downlights.



From the **TRILOGY COLLECTION:**
TRG51030Z

Trilogy COLLECTION

Collection S


FINISH:

Oil Bronze

SHADE:

Clear Seedy

TRG5105OZ DAMP



CLEAR
SEEDY
GLASS



Trilogy COLLECTION

PRODUCT

TRG5105OZ

DIMENSIONS

19" H, 26.5" W, 26.5" Dp.

CANOPY

5"

BULBS

5-60W Vintage Bulb Supplied*

*Max Wattage: 100W Med. Base or 23W CFL

Trilogy COLLECTION


FINISH:
o ld Bronze

GLASS:
Clear Seedy

DAMP TRG5103OZ



DAMP TRG1816OZ



DAMP TRG1508OZ






TRG1712OZ DAMP

CLEAR SEEDY GLASS

DAMP TRG1716OZ



TRG8701OZ DAMP



Trilogy COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TRG1508OZ	7.5" H*, 8" W, 8" Dp.	5"	-	1-60W Vintage Bulb Supplied**
TRG1712OZ	10" H, 12" W, 12" Dp.	5"	-	1-60W Vintage Bulb Supplied**
TRG1716OZ	12" H, 16" W, 16" Dp.	5"	-	3-60W Vintage Bulb Supplied**
TRG1816OZ	20" H, 16" W, 16" Dp.	5"	-	3-60W Vintage Bulb Supplied**
TRG5103OZ	17.5" H, 22" W, 22" Dp.	5"	-	3-60W Vintage Bulb Supplied**
TRG8701OZ	9.5" H, 8" W, 9" Ext	5" x 5"	3"	1-60W Vintage Bulb Supplied**

Chain-hung fixtures come with 8' of wire and 4' of chain.

*Comes with (2) 6" and (2) 12" Rods. All rod-hung fixtures come with 8' of wire.

**Max Wattage: 100W Med. Base or 23W CFL

Whitney COLLECTION

FINISH:
imperial Silver

SHADE:
White organza with Dark Grey trim

WHI5012IS   





WHI5009IS DAMP



DAMP **WHI8701IS**

Enlarged for detail



Whitney COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
WHI5009IS**	33" H, 32" W, 32" Dp.	6"	-	9-60W Cand. Base	5" x 4.5" x 5"
WHI5012IS**	38" H, 39" W, 39" Dp.	6"	-	12-60W Cand. Base	5" x 4.5" x 5"
WHI8701IS	16" H, 7" W, 7" Dp.	4.5" x 7"	12"	1-60W Cand. Base	5" x 4.5" x 5"

**Chain-hung fixtures come with 12' of wire and 8' of chain.





From the **WHITNEY COLLECTION**
Hanging Fixture: **WHI5005IS** Wall Fixture: **WHI8701IS**

Whitney COLLECTION

FINISH:
imperial Silver

SHADE:
White organza with Dark Grey trim

DAMP WHI5005IS



WHI1716IS **DAMP**

Whitney COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
WHI1716IS	16.5" H, 16" W, 16" Dp.	6"	-	3-60W Cand. Base	6" x 14.5" x 16"
WHI5005IS	27" H, 28" W, 28" Dp.	6.5"	-	5-60W Cand. Base	5" x 4.5" x 5"

Chain-hung fixtures come with 8' of wire and 4' of chain.



MINI-COLLECTIONS

QUOIZEL



From the **GRANT COLLECTION:**
GRT1508BN (p. 115)

*Photo courtesy of Dovetail Group LLC
and Terry Scholl Photography*

Adams COLLECTION

FINISH:

Leathered Bronze

SHADE:

White Linen Hardback

NEW!

FOR ♦ 2016

ADA5009LN DAMP



ADA5006LN 



 ADA2820LN



ADA8702LN 

Enlarged for detail

NEW!

FOR ♦ 2016

Adams COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
ADA2820LN	23" H*, 18.5" W, 18.5" Dp.	5"	-	4-100W Med. Base or 23W CFL	6" x 17" x 17"
ADA5006LN	10.5" H*, 25" W, 25" Dp.	5"	-	6-60W Cand. Base	5" x 5.5" x 5.5"
ADA5009LN	19.5" H**, 29.5" W, 29.5" Dp.	5"	-	9-60W Cand. Base	5" x 5.5" x 5.5"
ADA8702LN	13.5" H8, 12" W, 6" Ext.	5" x 5"	2.75"	2-60W Cand. Base	6" x 11.75" x 11.75"

*Rod-hung fixtures come with 10' of wire. **Rod-hung fixture comes with 12' of wire.
All rod hung fixtures come with 2 (6") and (2) 12" Rods.

Alexandria COLLECTION

FINISH:
Palladian Bronze


AX2826PN DAMP



AX2820PN DAMP



AX434PN DAMP



DANGLING
GLASS
ACCENTS

Alexandria COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
AX2820PN	8" H*, 19.5" W, 19.5" Dp.	.75" x 5"	5-100W Med. Base or 23W CFL
AX2826PN	14" H*, 26" W, 26" Dp.	.75" x 5"	6-100W Med. Base or 23W CFL
AX434PN	8" H**, 33.5" W, 15.5" Dp.	4.5"	4-100W Med. Base or 23W CFL

All rod-hung fixtures come with 10' of wire. *Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods.


Eastvale COLLECTION

MINI-Co Il eCt lo NS

FINISH:
Palladian Bronze

SHADE:
Metal

Pendant converts
to Semi-Flush Mount



EVE240PN

EVE2815PN



EVE1508PN

EVE1404PN

Eastvale COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
EVE1404PN	10.5" H, 36.5" W, 3.5" Dp.	5"	4-50W MR-16 with GU10 Shielded Bulb Supplied
EVE1508PN*	9.5" H**, 8" W, 8" Dp.	6"	1-100W Med. Base or 23W CFL
EVE240PN*	29" H**, 40" W, 14.5" Dp.	6"	2-100W Med. Base or 23W CFL
EVE2815PN*	12" H**, 14.5" W, 14.5" Dp.	6"	1-100W Med. Base or 23W CFL


*Rod-hung fixtures come with 8' of wire. **Comes with (2) 6" and (2) 12" Rods.

Chamber COLLECTION

FINISH:

Darkest Bronze

CHB5208DK



CHB5206DK




QUOIZEL
NATURALS
WOOD

CHB5204DK



CHB1612DK



Chamber COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
CHB1612DK	16" H, 12" W, 12" Dp.	5.5"	1-60W Vintage Bulb Supplied
CHB5204DK	21" H, 16" W, 16" Dp.	5.5"	4-60W Cand. Base
CHB5206DK	29" H, 24" W, 24" Dp.	5.5"	6-60W Cand. Base
CHB5208DK	35.5" H, 30.5" W, 30.5" Dp.	5.5"	8-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain. *Max Wattage: 1-100W Med. Base or 23W CFL.



Armelle COLLECTION

FINISH:

Imperial Bronze

SHADE:

Butterscotch o nyx

AME5018IB



QUOIZEL
NATURALS
ONYX

QUOIZEL
NATURALS
ONYX



AME5009IB DAMP



DAMP **AME8701IB**

Enlarged for detail



AME5005IB DAMP

Armelle COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
AME5005IB	23" H, 28" W, 28" Dp.	5"	-	5-60W Cand. Base
AME5009IB*	33" H, 33" W, 33" Dp.	5"	-	9-60W Cand. Base
AME5018IB*	48" H, 48" W, 48" Dp.	6"	-	18-60W Cand. Base
AME8701IB	9.5" H, 5" W, 6.5" Ext	4.63" x 7"	4"	1-60W Cand. Base

Chain-hung fixture comes with 8' of wire and 4' of chain. *Fixtures come with 12' of wire and 8' of chain.

Baron COLLECTION

FINISH:
Marcado Black

QUOIZEL
NATURALS
WOOD

BRO5203MK



BRO5204MK



BRO1715MK

Baron COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BRO1715MK	14.5" H, 15" W, 15" Dp.	5"	3-60W Cand. Base
BRO5203MK	27.5" H, 15.5" W, 15.5" Dp.	5"	3-60W Cand. Base
BRO5204MK	39" H, 18" W, 18" Dp.	5"	6-60W Cand. Base

All chain-hung fixtures come with 12' of wire and 8' of chain.

Castile COLLECTION

MINI-Co l l eCt lo NS

FINISH:
Rustic Black

QUOIZEL
NATURALS
WOOD

DAMP CS5012RK



DAMP CS1718RK

DAMP CS5006RK



Castile COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
CS1718RK	15.5" H, 18" W, 18" Dp.	5" x 0.75"	4-60W Cand. Base
CS5006RK*	22.5" H, 29" W, 29" Dp.	5" x 0.75"	6-60W Cand. Base
CS5012RK**	27" H, 35.5" W, 35.5" Dp.	6.5" x 1.25"	12-60W Cand. Base

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.



From the **MILBANK COLLECTION:**
MBK5005VG

Milbank COLLECTION

MINI-Collection NS

FINISH:
Vintage Gold

GLASS:
opal etched

MBK5005VG



MBK2820VG



MBK1716VG



Milbank COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MBK1716VG	11" H, 16" W, 16" Dp.	5.5"	3-100W Med. Base or 23W CFL
MBK2820VG	26" H, 20.5" W, 20.5" Dp.	5.5"	4-100W Med. Base or 23W CFL
MBK5005VG	26.5" H, 25" W, 25" Dp.	5.25"	5-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

Grant COLLECTION

FINISH:

BN Brushed Nickel

IS Imperial Silver

PN Palladian Bronze

GLASS: opal etched

Available in Three Finishes!


GRT5103IS



GRT5103PN



DAMP **GRT5103BN**



Pendant converts
to Semi-Flush Mount



(all finishes)

GRT2814PN DAMP

DAMP **GRT2814BN**

DAMP **GRT1508IS**

DAMP **GRT1508BN**

Grant COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
GRT1508BN/IS/PN	9.5" H*, 8" W, 8" Dp.	5"	1-100W Med. Base or 23W CFL
GRT2814BN/IS/PN	11.5" H*, 13.5" W, 13.5" Dp.	5"	1-100W Med. Base or 23W CFL
GRT5103BN/IS/PN	15.5" H*, 24" W, 24" Dp.	5"	3-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with 2 (6)" and (2) 12" Rods.

Laila COLLECTION

FINISH:

Rustic Antique Bronze

LLA5205RA DAMP



LLA5204RA DAMP



LLA5203RA DAMP



LLA1615RA DAMP



Laila COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
LLA1615RA	14.5" H, 15" W, 15" Dp.	8"	3-60W Cand. Base
LLA5203RA*	20" H, 15" W, 15" Dp.	5.5"	3-60W Cand. Base
LLA5204RA**	21" H, 18" W, 18" Dp.	5"	4-60W Cand. Base
LLA5205RA**	26.5" H, 22" W, 22" Dp.	5.5"	5-60W Cand. Base

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.

Metropolis COLLECTION

MINI-Collection NS

FINISH: Antique Nickel
SHADE: Metal with Inneropal etched Glass



NEW!
FOR 2016

Pendant converts to Semi-Flush Mount

MTP5203AN DAMP
Enlarged for detail

MTP1510AN DAMP

MTP2820AN DAMP

Pendant converts to Semi-Flush Mount

MTP1718AN DAMP

Metropolis COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MTP1510AN	12" H, 10" W, 10" Dp.	5"	1-100W Med. Base or 23W CFL
MTP1718AN	9" H, 18" W, 18" Dp.	.75" x 7.75"	3-75W Med. Base or 18W CFL
MTP2820AN	9" H, 20" W, 20" Dp.	4.75"	3-100W Med. Base or 23W CFL
MTP2823AN	9" H, 23" W, 23" Dp.	4.75"	4-100W Med. Base or 23W CFL
MTP5203AN*	20" H, 16" W, 16" Dp.	4.75"	3-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8" of wire. Comes with (2) 6" and (2) 12" Rods. **Comes with 12" of wire.

New England COLLECTION

FINISH:

BN Brushed Nickel

PN Palladian Bronze

GLASS:

Acid etched

NA5103BN DAMP





NA1510BN **DAMP**



NA1514BN **DAMP**



NA8414PN **WET**



WET NA8409PN

**INDOOR
OUTDOOR**

NewEngland COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
NA1510BN	11" H*, 9.5" W, 9.5" Dp.	5.25"	-	1-100W Med. Base or 23W CFL
NA1514BN	9.5" H*, 14" W, 14" Dp.	5.25"	-	1-100W Med. Base or 23W CFL
NA5103BN	22.5" H, 25" W, 25" Dp.	5"	-	3-100W Med. Base or 23W CFL
NA8409PN	9.5" H, 9.5" W, 10" Dp.	5.25" x 5.25"	4.5"	1-100W Med. Base or 23W CFL
NA8414PN	11.5" H, 14.5" W, 15.5" Dp.	7" x 7"	5.5"	1-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire.
*Comes with (2) 6" and (2) 12" Rods.

Favern COLLECTION

FINISH:

Darkest Bronze

TVN5005DK



VINTAGE STYLE
bulb included



QUOIZEL
**NATURALS
WOOD**

TVN232DK



TVN1717DK

Favern COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
TVN1717DK	14.5" H, 17" W, 17" Dp.	5.5"	3-60W Vintage Bulbs Supplied†
TVN232DK	10.5" H*, 32" W, 12" Dp.	10.5" x 4.5"	6-60W Vintage Bulbs Supplied†
TVN5005DK	13" H**, 26" W, 26" Dp.	6"	5-60W Vintage Bulbs Supplied†

Rod-hung fixtures come with 8' of wire. *Comes with (4) 6" and (4) 12" Rods. **Comes with (2) 6" and (2) 12" Rods.
†Max Wattage: 100W Med. Base or 23W CFL.

Mini-Collection S



From the **TAVERN COLLECTION: TVN232DK**

Palmer COLLECTION

FINISH:

Palladian Bronze

SHADE:

Outer: Light Amber Organza with Brown trim
Inner: etched Glass

PLR5005PN DAMP



PLR2820PN DAMP



DAMP PLR1716PN



Palmer COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
PLR1716PN	14.5" H, 16" W, 16" Dp.	4.75"	3-100W Med. Base or 23W CFL
PLR2820PN	23.5" H, 20" W, 20" Dp.	5"	3-100W Med. Base or 23W CFL
PLR5005PN	21" H, 25" W, 25" Dp.	5"	5-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

RemiCOLLECTION

MINI-Collection NS

FINISH:
Polished Chrome

SHADE:
White Fabric

REM345C DAMP



DAMP **REM5004C**



REM8701C DAMP

Enlarged for detail

RemiCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
REM345C	10" H, 44.5" W, 5.5" Dp.	4.5" Sq.	-	3-75W Med. Base or 18W CFL	6" x 10.5" x 5.5"
REM5004C	13.5" H*, 29" W, 29" Dp.	4.5" Sq.	-	4-75W Med. Base or 18W CFL	6" x 10.5" x 5.5"
REM8701C	11" H, 10.5" W, 6.5" Dp.	4.5" Sq.	8.5"	1-60W Med. Base or 13W CFL	6" x 10.5" x 5.5"

Cable-hung fixture comes with 12' of wire. Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

Odell COLLECTION

FINISH:
Imperial Bronze

SHADE:
Metal Mesh

QUOIZEL
NATURALS
WOOD

NEW!

FOR ♦ 2016

ODL5009IB DAMP





ODL5005IB DAMP

DAMP **ODL5206IB**

NEW!
FOR ♦ 2016

QUOIZEL
NATURALS
WOOD



Pendant converts to Semi-Flush Mount




ODL2820IB DAMP



ODL5303IB DAMP

Metal Mesh is quickly becoming a popular material in home lighting, for a dramatic and contemporary diffused look.



Odell COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ODL2820IB	30" H, 20" W, 20" Dp.	1.25" x 6"	5-60W Cand. Base
ODL5005IB	29.5" H, 28.5" W, 28.5" Dp.	1.5" x 6"	5-60W Cand. Base
ODL5009IB*	39" H, 33.5" W, 33.5" Dp.	1.5" x 6"	9-60W Cand. Base
ODL5206IB*	41" H, 18" W, 18" Dp.	1.5" x 6"	6-60W Cand. Base
ODL5303IB	16.5" H, 16" W, 16" Dp.	5"	3-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Fixtures come with 12' of wire and 8' of chain.

OperaCOLLECTION

FINISH:
Western Bronze

NEW!

FOR ♦ 2016

DAMP OPA5005WT



OPA5304WT DAMP

NEW!

FOR ♦ 2016

FAUX PEARL ACCENTS



OPA1617WT DAMP

DAMP OPA1613WT



Opera COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
OPA1613WT	10" H, 13" W, 13" Dp.	8"	3-60W Cand. Base
OPA1617WT	10" H, 17.5" W, 17.5" Dp.	10"	4-60W Cand. Base
OPA5005WT	23.5" H, 22.5" W, 22.5" Dp.	5.5"	5-60W Cand. Base
OPA5304WT	17" H, 17" W, 17" Dp.	5.5"	4-60W Cand. Base

All chain-hung fixtures come with 8' of wire and 4' of chain.

Noble COLLECTION

FINISH:
Rustic Black

DAMP NBE5009RK

SOLID WOOD
CANDLE
HOLDERS





DAMP NBE5008RK



DAMP NBE8702RK



NBE5303RK **DAMP**



NBE5005RK **DAMP**

Noble COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
NBE5005RK*	25.5" H, 24" W, 24" Dp.	1" x 5"	-	5-60W Cand. Base
NBE5008RK*	31" H, 32" W, 32" Dp.	5"	-	8-60W Cand. Base
NBE5009RK**	36" H, 32" W, 32" Dp.	5"	-	9-60W Cand. Base
NBE5303RK*	19.5" H, 15" W, 15" Dp.	5"	-	3-60W Cand. Base
NBE8702RK	13" H, 11.5" W, 8" Dp.	5" x 5"	2.5"	2-60W Cand. Base

*Fixture comes with 8' of wire and 4' of chain. **Chain-hung fixture comes with 12' of wire and 8' of chain.

Sophia COLLECTION

FINISH:**BN** Brushed Nickel**PN** Palladian Bronze**GLASS:**

etched Glass Painted White Inside

SPH5009BN 

Sophia COLLECTION

PRODUCT

SPH5009BN/PN

DIMENSIONS

33.5" H, 32" W, 32" Dp.

CANOPY

5.75"

BULBS

9-100W Med. Base or 23W CFL

Fixture comes with 12' of wire and 8' of chain.



Sophia COLLECTION

FINISH:

- BN** Brushed Nickel
- PN** Palladian Bronze

GLASS:

etched Glass Painted White Inside



SPH1508PN DAMP

Enlarged for detail



SPH5005PN DAMP

*CLASSIC
CONTEMPORARY
CURVES*

Sophia COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SPH1508BN/PN	5" H*, 8" W, 8" Dp.	5.75"	-	1-100W Med. Base or 23W CFL
SPH5005BN/PN	23" H, 26.5" W, 26.5" Dp.	5.5"	-	5-100W Med. Base or 23W CFL


Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

NewHarborCOLLECTION

MINI-Co l l eCt lo NS

FINISH:
Western Bronze

DAMP NHR1718WT



DAMP NHR5204WT



DAMP NHR538WT



NewHarborCOLLECTION


PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
NHR1718WT	10.5" H, 18" W, 18" Dp.	4.75"	4-60W Vintage Bulbs Supplied
NHR5204WT†	23.5" H*, 14" W, 14" Dp.	5" Sq.	4-60W Vintage Bulbs Supplied
NHR538WT††	9.5" H**, 38" W, 12" Dp.	.75" x 4.75" x 9"	5-60W Vintage Bulbs Supplied

*Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods. †Fixture comes with 12' of wire. ††Fixture comes with 8' of wire.
Max Wattage: 100W Med. Base or 23W CFL.

Wilder COLLECTION

FINISH:
Mottled Black

DAMP WLR5204MB





WLR2820MB DAMP



DAMP **WLR1506MB**



DAMP **WLR1716MB**



Wilder COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
WLR1506MB	8.5" H*, 6" W, 6" Dp.	5"	1-60W Vintage Bulb Supplied
WLR1716MB	13.5" H, 16" W, 16" Dp.	5"	3-60W Vintage Bulbs Supplied
WLR2820MB†	24.5" H, 20.5" W, 20.5" Dp.	5"	4-60W Vintage Bulbs Supplied
WLR5204MB††	33" H, 16" W, 16" Dp.	5"	4-60W Vintage Bulbs Supplied

†Chain-hung fixture comes with 8' of wire and 4' of chain. ††Fixture comes with 12' of wire and 8' of chain. Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. Max Wattage: 100W Med Base or 23W CFL.

Tricia COLLECTION

FINISH:
Vintage Silver

   **TCA5009VP**



GLASS
DROPS



TCA8701VP DAMP

DAMP TCA5006VP



TCA5004VP DAMP

Tricia COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TCA5004VP*	31.5" H, 21" W, 21" Dp.	7"	-	4-60W Cand. Base
TCA5006VP*	36" H, 27" W, 27" Dp.	7"	-	6-60W Cand. Base
TCA5009VP**	41.5" H, 31" W, 31" Dp.	7"	-	9-60W Cand. Base
TCA8701VP	24.5" H, 3" W, 6.5" Ext.	4.5" x 11.5"	9.5"	1-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.


UnionStation COLLECTION

FINISH:

Western Bronze

SHADE:

Metal Mesh



DAMP UST5003WT

BRASS ACCENTS



UnionStation COLLECTION

PRODUCT

UST5003WT

DIMENSIONS

20" H, 28" W, 28" Dp.

CANOPY/BACKPLATE

5"

BULBS

3-60W Vintage Bulb + 1-50W MR-16 w/GU10 Base Shielded (Supplied)**

Chain-hung fixture comes with 8' of wire and 4' of chain.



From the **UNION STATION COLLECTION**: UST5003WT

UnionStation COLLECTION


FINISH:

Western Bronze

SHADE:

Metal Mesh

DAMP UST1505WT



UST6127WT 

DAMP UST1716WT



UnionStation COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS	SHADE DIMS.
UST1505WT	8" H*, 5" W, 5" Dp.	5"	1-60W Vintage Bulb Supplied**	-
UST1716WT	11.5" H, 16" W, 16" Dp.	5.5"	3-60W Vintage Bulb Supplied**	-
UST6127WT	26.5" H, 15.5" W, 15.5" Dp.	-	1-60W Vintage Bulb Supplied**	15.5" x 15.5" x 9"

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

**Max Wattage: 100W Med. Base or 23W CFL.



LAKESIDE: LKE5204VG (p. 168)

*D*INING & FOYER
and More!

QUOIZEL


Auburn COLLECTION

FINISH:
Rustic Black



ABN5024RK

QUOIZEL
NATURALS
WOOD



Auburn COLLECTION

PRODUCT

ABN5024RK

DIMENSIONS

45" H, 48" W, 48" Dp.

CANOPY

5.5"

BULBS

24-60W Cand. Base

Chain-hung fixture comes with 12' of wire and 8' of chain.

dINING & FOYER



From the **AUBURN COLLECTION:**
ABN5006RK

Auburn COLLECTION

FINISH:
Rustic Black

ABN5012RK

WALNUT STAIN
HIGHLIGHTS



QUOIZEL
NATURALS
WOOD

ABN5006RK

Auburn COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ABN5006RK	28" H, 28" W, 28" Dp.	5"	6-60W Cand. Base
ABN5012RK*	31" H, 36" W, 36" Dp.	5"	12-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Comes with 12' of wire and 8' of chain.

Mirren COLLECTION

d INING & FOYER

FINISH:
Imperial Bronze

MRN5008IB



MRN5006IB



MRN5005IB



Mirren COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MRN5005IB	18" H, 21" W, 21" Dp.	5"	5-60W Cand. Base
MRN5006IB	23" H, 28" W, 28" Dp.	5"	6-60W Cand. Base
MRN5008IB	28" H, 32" W, 32" Dp.	5"	8-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

Castle Hill COLLECTION

FINISH:

Antique Nickel

NEW!

FOR ♦ 2016

DAMP CTH5009AN



detail





CTH5006AN DAMP



NEW!
FOR ♦ 2016

DAMP **CTH5003AN**



DAMP **CTH5204AN**

CastleHill COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
CTH5003AN	20.5" H, 19" W, 19" Dp.	5"	3-60W Cand. Base
CTH5006AN	24.5" H, 25" W, 25" Dp.	5"	6-60W Cand. Base
CTH5009AN*	33" H, 31" W, 31" Dp.	5"	9-60W Cand. Base
CTH5204AN*	30" H, 16.5" W, 16.5" Dp.	5"	4-60W Cand. Base


Chain-hung fixtures come with 8' of wire and 4' of chain. *Fixtures come with 12' of wire and 8' of chain.

Voyager COLLECTION

FINISH:
Malaga

DAMP VYR5024ML

TAPERED
METAL CANDLE
SLEEVES





DAMP VYR5012ML



DAMP VYR5006ML



DAMP VYR5008ML

Voyager COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
VYR5006ML*	26" H, 28" W, 28" Dp.	6"	6-60W Cand. Base
VYR5008ML*	28" H, 36" W, 20" Dp.	5"	8-60W Cand. Base
VYR5012ML**	36" H, 36" W, 36" Dp.	5"	12-60W Cand. Base
VYR5024ML**	52" H, 48" W, 48" Dp.	6"	24-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Chain-hung fixtures come with 12' of wire and 8' of chain.



From the **CARRABELLE COLLECTION:**
QMC1199FR

Carrabelle COLLECTION

d INING & FOYER

FINISH:
French Bronze

QMC1199FR



CRE5004FR



OPTIC
CRYSTAL

Carrabelle COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE	SHADE DIMS.
CRE5004FR	24" H, 24" W, 24" Dp.	5.5"	4-60W Cand. Base	Silver Organza Chiffon	7" x 21" x 24"
QMC1199FR	23.5" H, 18" W, 18" Dp.	5.5"	5-60W Cand. Base	-	-

Chain-hung fixtures come with 8' of wire and 4' of chain.

Wesley COLLECTION

FINISH:
Italian Fresco



WSY5012IF



WSY5008IF



WSY5005IF



Wesley COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
WSY5005IF*	27" H, 26" W, 26" Dp.	5"	5-60W Cand. Base
WSY5008IF*	30" H, 30" W, 30" Dp.	5.5"	8-60W Cand. Base
WSY5012IF**	36" H, 36" W, 36" Dp.	7"	12-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.

Estate COLLECTION

FINISH:
Imperial Bronze

DAMP EST5208IB

NEW!
FOR ♦ 2016

EST5204IB **DAMP**



DAMP EST5206IB



SWIRLED CAST
IRON ARMS

Estate COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
EST5204IB	29.5" H, 13.5" W, 13.5" Dp.	5"	4-60W Cand. Base
EST5206IB	44.5" H, 19.5" W, 19.5" Dp.	5"	6-60W Cand. Base
EST5208IB	53.5" H, 26.5" W, 26.5" Dp.	5"	8-60W Cand. Base

Chain-hung fixtures come with 12" of wire and 8' of chain.



DUN5204GK DAMP

Dunn

FINISH: Grey Ash

NEW!

FOR ♦ 2016



DAMP DUN5203GK

Woodrow

FINISH: Rustic Black



QF1839RK DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
DUN5203GK	22.5" H, 13" W, 13" Dp.	5"	3-60W Cand. Base
DUN5204GK	27" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
QF1839RK	22" H, 12" W, 12" Dp.	5.5"	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain

Silhouette COLLECTION

FINISH:
Italian Fresco

SHADE:
Sliver Organza Chiffon

SLT5006IF DAMP

CRYSTAL
TEARDROPS



SLT5004IF DAMP



DAMP **SLT5303IF**

Silhouette COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
SLT5004IF	28" H, 24" W, 24" Dp.	5.5" x 1"	4-60W Cand. Base	6.5" x 24" x 24"
SLT5006IF	33.5" H, 28" W, 28" Dp.	5.5" x 1"	6-60W Cand. Base	9" x 30" x 30"
SLT5303IF	24" H, 18" W, 18" Dp.	5.5" x 1"	3-60W Cand. Base	6" x 18" x 18"


Chain-hung fixtures come with 8' of wire and 4' of chain.

Belhaven COLLECTION

d in in G & Foyer

FINISH:
Vintage Gold

SHADE:
Mica Shade with Black t rim



detail

QUOIZEL
NATURALS
MICA

BHN5009VG

BHN5006VG

NEW!
FOR ♦ 2016

BHN5303VG



Belhaven COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BHN5006VG	23" H*, 27" W, 27" Dp.	5"	6-60W Cand. Base
BHN5009VG**	30" H*, 31" W, 31" Dp.	5"	9-60W Cand. Base
BHN5303VG	15.5" H*, 16.5" W, 16.5" Dp.	5"	3-60W Cand. Base

*Rod-hung fixtures come with 8' of wire. **Fixture comes with 12' of wire. All rod-hung fixtures come with (2) 6" and (2) 12" Rods.



From the **ALSTON COLLECTION:**
QMC404B0

Miramar

FINISH: Polished Chrome
GLASS: Crystal Glass Accents



NEW!
FOR ♦ 2016

MMR5303C DAMP

Majesty

FINISH: Vintage Gold



DAMP **MJY5304VG**

Aston

FINISH: Bolivian Bronze



DAMP **QMC404BO**

See matching semi-flush
MJY1615VG on page 296.

PRODUCT	DIMENSIONS	CANOPY	BULBS
MJY5304VG	19" H, 12" W, 12" Dp.	5"	4-60W Cand. Base
QMC404BO*	21" H, 18" W, 18" Dp.	5"	4-60W Cand. Base
MMR5303C	19.5" H, 12.5" W, 12.5" Dp.	5"	3-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Comes with 12' of wire and 8' of chain.

QUOIZEL
NATURALS
ROPE



Sandelier
FINISH: Imperial Bronze

BDR5006IB DAMP

DAMP **WDM5005WT**

See matching pendant **BDR2820IB** in the Quoizel Naturals section on page 238.

QUOIZEL
NATURALS
WOOD



Wyndmoor
FINISH: Western Bronze

CP5006IB DAMP

HAND FORGED
ACCENTS



Capri
FINISH: Imperial Bronze

See matching pendant **CP2820IB** on page 268.

PRODUCT	DIMENSIONS	CANOPY	BULBS
BDR5006IB	24" H, 26" W, 26" Dp.	5.5"	6-60W Cand. Base
CP5006IB	22" H*, 32" W, 16.5" Dp.	.75" x 5"	6-60W Cand. Base
WDM5005WT	30" H, 28" W, 28" Dp.	5"	5-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.
Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Ridge Manor

FINISH: Mottled Black



QF1820MB DAMP

Collins

FINISH: Masterpiece



DAMP QF1402CMU

Frontier

FINISH: Imperial Bronze



FTR5204IB DAMP

See matching semi-flush
FTR1713IB on page 288.

PRODUCT	DIMENSIONS	CANOPY	BULBS
FTR5204IB	23.5" H*, 13" W, 13" Dp.	5"	4-60W Cand. Base
QF1402CMU	29.5" H, 16.5" W, 16.5" Dp.	5.5"	4-60W Cand. Base
QF1820MB	27" H, 18" W, 18" Dp.	6"	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain.
Rod-hung fixtures come with 12' of wire. *Comes with (2) 6" and (2) 12" Rods.

Celestial

FINISH: Brushed Nickel
GLASS: Opal Etched

See matching semi-flush
CLT1714BN on page 289.

DAMP **CLT5004BN**



DAMP **KPR5005BN**



Kemper

FINISH: Brushed Nickel
GLASS: Etched Painted White Inside

DOWNLIGHT

DAMP **AML5005OZ**



NEW!

FOR ♦ 2016

See matching pendant
AML2821OZ on page 265.

Amelia

FINISH: Old Bronze
GLASS: Etched Painted White Inside

PRODUCT	DIMENSIONS	CANOPY	BULBS
AML5005OZ	30" H, 28.5" W, 28.5" Dp.	1.5" x 5.75"	5-100W Med. Base or 23W CFL
CLT5004BN	16" H*, 25" W, 25" Dp.	5"	4-100W Med. Base or 23W CFL
KPR5005BN	18.5" H*, 25" W, 25" Dp.	6.5"	5-100W Med. Base or 23W CFL + 1-50W MR16 GU10 Shielded Supplied

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Serenity COLLECTION

d INING & FOYER

FINISH:
Italian Fresco

DAMP SER5009IF



DAMP SER5006IF



DAMP SER5004IF



Serenity COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
SER5004IF*	24" H, 20" W, 20" Dp.	1.25" x 5"	4-60W Cand. Base
SER5006IF*	27.5" H, 26.5" W, 26.5" Dp.	1.25" x 5"	6-60W Cand. Base
SER5009IF**	34" H, 30" W, 30" Dp.	5"	9-60W Cand. Base

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.

Majestic COLLECTION

FINISH: Brushed Nickel

GLASS: Crystal Accents

NEW!

FOR ♦ 2016

DAMP MJT5008BN



detail



NEW!
FOR ♦ 2016



MJT5006BN DAMP

*CRYSTAL GLASS
ACCENTS*



DAMP **MJT5004BN**

*Majestic*COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MJT5004BN	19.5" H, 15" W, 15" Dp.	5"	4-60W Cand. Base
MJT5006BN	26.5" H, 22.5" W, 22.5" Dp.	5"	6-60W Cand. Base
MJT5008BN	31" H, 27.5" W, 27.5" Dp.	5"	8-60W Cand. Base + 1 -60 W Clear G9 Xenon

Chain-hung fixtures come with 8' of wire and 4' of chain.

DAMP

HK5008TC

Holbrook

FINISH: tuscan Brown



QUOIZEL
NATURALS
WOOD

HK5005TC

DAMP



DAMP

QF1840RK



Planter

FINISH: Rustic Black

QUOIZEL
NATURALS
WOOD

PRODUCT

DIMENSIONS

CANOPY

BULBS

HK5005TC

14" H, 24" W, 24" Dp.

5.5"

5-60W Cand. Base

HK5008TC

19.5" H, 29" W, 29" Dp.

5.5"

8-60W Cand. Base


QF1840RK*

26" H, 12.5" W, 12.5" Dp.

5"

3-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. *Fixture comes with 12' of wire and 8" of chain.



Thornhill

FINISH: Mercado Black

Pendant converts to Semi-Flush Mount



NEW!
FOR ♦ 2016

THL5006MK



THL1718MK

Menlo

FINISH: Western Bronze

NEW!
FOR ♦ 2016

MOVABLE ARMS



detail

See matching bath fixtures
MNO8602,3,4 IS on page 357.

MNO5006WT

PRODUCT	DIMENSIONS	CANOPY	BULBS
MNO5006WT	14" H*, 28" W, 28" Dp.	5"	6-60W Vintage Bulbs Supplied**
THL1718MK	16.5" H, 18" W, 18" Dp.	5"	4-40W Vintage Bulbs Supplied†
THL5006MK	27" H, 26" W, 26" Dp.	5"	6-40W Vintage Bulbs Supplied†

Chain-hung fixtures come with 8' of wire and 4' of chain. All rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
**Max Wattage: 100W Med Base or 23W CFL. †Max Wattage: 60W Cand. Base.

Lakeside

FINISH: Vintage Gold
GLASS: Clear Water

NEW!

FOR ♦ 2016



LKE5204VG DAMP

Colton

FINISH: Western Bronze
GLASS: Antique Mercury

NEW!

FOR ♦ 2016



DAMP CTO5204WT

DAMP GCT5204WT



NEW!

FOR ♦ 2016

Grand Court

FINISH: Western Bronze
GLASS: Clear Beveled

PRODUCT	DIMENSIONS	CANOPY	BULBS
CTO5204WT	18" H*, 17" W, 17" Dp.	5.5"	4-60W Cand. Base
GCT5204WT	23.5" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
LKE5204VG	31.5" H, 15" W, 15" Dp.	5"	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain. Rod-hung fixture comes with 12' of wire. *Comes with (2) 6" and (2) 12" Rods

Sabrina

FINISH: Vintage Gold
GLASS: Beveled Crystal



NEW!
FOR ♦ 2016

SRA5204VG

Kayden

FINISH: Brushed Nickel
GLASS: Clear Seedy



QUOIZEL
NATURALS
WOOD

KDN5004BN

See matching
mini pendant
KDN1510BN
on page 280.

UNS5204IB



Unison

FINISH: Imperial Bronze

NEW!
FOR ♦ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
KDN5004BN	18.5" H*, 19.5" W, 19.5" Dp.	5"	4-60W Cand. Base
SRA5204VG**	26" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
UNS5204IB†	26" H, 20" W, 20" Dp.	6"	4-60W Cand. Base

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

**Chain-hung fixture comes with 12' of wire and 8' of chain. †Chain-hung fixture comes with 8' of wire and 4' of chain.

DAMP

PB5004TK



embroke

FINISH: tarnished Bronze

NEW!

FOR ♦ 2016

QUOIZEL
NATURALS
ROPE

PB5008TK

DAMP



DAMP

BGS5203RK



NEW!

FOR ♦ 2016

Burgess

FINISH: Rustic Black

GLASS: Mercury Glass

See matching semi-flush
BGS1715RK on page 288.

PRODUCT	DIMENSIONS	CANOPY	BULBS
BGS5203RK	24.5" H, 15" W, 15" Dp.	5"	3-60W Cand. Base
PB5004TK	23" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
PB5008TK	32" H, 22.5" W, 22.5" Dp.	5"	8-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

DAMP ANR5010IB



Anchor

FINISH: Imperial Bronze

QUOIZEL
NATURALS
WOOD

VINTAGE STYLE
bulb included



ANR5006IB **DAMP**

Knottin

FINISH: **VG** Vintage Gold
WT Western Bronze



Also available in Vintage Gold:
QF1829VG



QF1829WT **DAMP**

VINTAGE STYLE
bulb included



PRODUCT	DIMENSIONS	CANOPY	BULBS
ANR5006IB*	24.5" H**, 22.5" W, 22.5" Dp.	5"	6-60W Vintage Bulb Supplied†
ANR5010IB*	27.5" H**, 28" W, 28" Dp.	5"	10-60W Vintage Bulb Supplied†
QF1829WT/VG††	22" H**, 18.5" W, 18.5" Dp.	4.75"	4-60W Vintage Bulb Supplied†

*Rod-hung fixture comes with 8' of wire. **Comes with (2) 6" and (2) 12" Rods. †Max Wattage: 100W Med. Base or 23W CFL.

††Rod-hung fixtures come with 12' of wire.

PLATINUM

by QUOIZEL



From the **RIBBONS COLLECTION:**
RBN2823SG (p.189)



The Platinum Collection is an exciting platform of contemporary design – playful and dramatic expressions in lighting. This collection utilizes energy-efficient light sources like G9 and G4 (low-voltage) bulbs, creating a dramatic effect through the intensity of light which showcases the refractive qualities of cut crystal.

Bordeaux COLLECTION

FINISH:

Polished Chrome

GLASS:

BRX Clear Crystal

BRXA Amber Crystal **NEW!**

DAMP BRX2818C

BEAUTIFULLY
CUT CRYSTALS



detail



CRYSTAL ♦ COLLECTION

- ◆ Dramatic lighting created by faceted crystal pendants
- ◆ Free of contaminant colors such as iron for clarity and purity allowing the light to radiate to its greatest potential
- ◆ Bulbs are positioned in the most strategic locations, maximizing the radiance of the light emanating through the crystal
- ◆ Highly polished mirrored chrome maximizes the reflectivity of the projected light
- ◆ The highest quality G4 and G9 bulbs create a great intensity of light



DAMP BRX1619C



DAMP BRX1614C

DAMP BRXA1619C



DAMP BRXA1614C



NEW!
FOR ♦ 2016

Bordeaux COLLECTION

PRODUCT	DIMENSIONS	CANOPIY	BULBS
BRX1614C	8" H, 14" W, 14" Dp.	14"	4-40W Clear G9 Xenon Supplied
BRX1619C	8" H, 19.5" W, 19.5" Dp.	17.75" x 1"	5-40W Clear G9 Xenon Supplied
BRX2818C*	8" H, 17.5" W, 17.5" Dp.	4.75" x 1"	5-40W Clear G9 Xenon Supplied
BRXA1614C	8" H, 14" W, 14" Dp.	14"	4-40W Clear G9 Xenon Supplied
BRXA1619C	9" H, 20" W, 20" Dp.	17.75" x 1"	5-40W Clear G9 Xenon Supplied

*Fixture comes with 8" of wire.

Bordeaux COLLECTION

FINISH:

Polished Chrome

GLASS:

Clear Crystal

BRX1626C



BRX1611C



PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION

NEW!

FOR ♦ 2016

BRX1620C



Bordeaux COLLECTION

PRODUCT

DIMENSIONS

CANOPY

BULBS

BRX1611C

8" H, 12" W, 12" Dp.

9.75"

4-40W Clear G9 Xenon Supplied

BRX1620C

10.5" H, 20" W, 20" Dp.

17.25"

6-40W Clear G9 Xenon Supplied

BRX1626C

8.5" H, 25.5" W, 25.5" Dp.

23.5" x 1"

7-40W Clear G9 Xenon Supplied



PLATINUM CRYSTAL LEAF
PCCF2824C (p. 180)

Galaxy COLLECTION

FINISH:
Polished Chrome

DAMP PCGX1817C



DAMP 50 PCGX1826C



PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION

Galaxy COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCGX1817C*	38" H, 17.5" W, 17.5" Dp.	5.875"	5-50W , MR16 GU10 Shielded Supplied
PCGX1826C**	53" H, 26" W, 30" Dp.	5.875"	7-50W , MR16 GU10 Shielded Supplied

*Fixture comes with 8' of wire. **Fixture comes with 10' of wire.



PCCT1616C DAMP

PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

Countess

FINISH: Polished Chrome



DAMP PCCT1623C



PCAX1714C DAMP

Alexa

FINISH: Polished Chrome

SHADE: Crystal

See matching bath products
on page 195.

NEW!

FOR ♦ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCAX1714C	8.5" H, 14" W, 14" Dp.	1" x 6"	3-100W Med. Base or 23W CFL
PCCT1616C	8.5" H, 16.5" W, 16.5" Dp.	13.75"	9-20W Clear G4 XENON Supplied
PCCT1623C	8" H, 23" W, 23" Dp.	19.5"	18-20W Clear G4 XENON Supplied




Crowne

FINISH: Polished Chrome

GLASS: Crystal Accents

DAMP PCCR1717C



detail

NEW!
FOR ♦ 2016

DAMP PCCF2824C

Crystal Leaf

FINISH: Polished Chrome

GLASS: Crystal Accents

PCAN2814C **DAMP**



Arena

FINISH: Polished Chrome

SHADE: Crystal-Lined Metal Bands



PRODUCT	DIMENSIONS	CANOPY	BULBS
PCAN2814C*	10.5" H, 14" W, 14" Dp.	6"	6-20W Clear G4 XENON Supplied
PCCF2824C**	24" H, 24" W, 24" Dp.	1" x 7.5"	8-40W Clear G9 XENON Supplied
PCCR1717C	11" H, 16.5" W, 16.5" Dp.	4.75"	4-40W Clear G9 XENON Supplied

*Fixture comes with 6' of wire. **Fixture comes with 8' of wire.

Mercury

FINISH: Polished Chrome
SHADE: Metal with Crystal Drops

 PCMY2818C



1,000's OF
CRYSTAL DROPS

NEW!
FOR ♦ 2016

INDIVIDUAL
CRYSTALS INSIDE
CLEAR GLASS

Treasure

FINISH: Polished Chrome
GLASS: Clear

 PCTS1503C



PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

Shimmer

FINISH: Polished Chrome
GLASS: Studded Crystal

See matching bath products
on page 194.



 PCSR1716C

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCMY2818C	5.5" H, 18" W, 18" Dp.	1" x 5.5"	6-60W Clear G9 XENON Supplied
PCSR1716C	7" H, 18" W, 18" Dp.	6.75"	3-40W Clear G9 XENON Supplied
PCTS1503C	6" H, 3" W, 3" Dp.	1" x 4.75"	1-25W Clear G9 XENON Supplied

All cable-hung fixtures come with 8' of wire.

DAMP PCVN2820C



Vision
FINISH: Polished Chrome
GLASS: Clear n oodle



DAMP PCVN1716C

NEW!
FOR ♦ 2016

PLATINUM
 by QUOIZEL
 CRYSTAL ♦ COLLECTION

Paragon
FINISH: Polished Chrome

*See matching bath products
 on page 193.*

DAMP PRN1614C



PRODUCT	DIMENSIONS	CANOPY	BULBS
PCVN1716C	13" H, 16" W, 16" Dp.	1" x 5.5"	4-60W Clear G9 XENON Supplied
PCVN2820C	5.5" H*, 20.5" W, 20.5" Dp.	1" x 5.5"	5-60W Clear G9 XENON Supplied
PRN1614C	6" H, 14.5" W, 14.5" Dp.	-	4-40W Clear G9 XENON Supplied

Fixtures comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.



PCHE1620C

Highrise

FINISH: Polished Chrome



PCHE1616C

INTEGRATED LED
10 YEAR WARRANTY

Janelle

FINISH: Polished Chrome
GLASS: Frosted, Sandblasted inside
SHADE: organza with Silver Trim

PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

LED CHART

	PCJL2820C	PCHE1616C	PCHE1620C
Lumens	3080	2040	1080
Total Watts	37W	24W	10.8W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3100K	3000K	3000K
Dimmable	No	Yes	Yes



ILLUMINATED
CRYSTAL RING

PCJL2820C

PRODUCT	DIMENSIONS	CANOPY	LIGHT SOURCE/ BULB
PCHE1616C	11" H, 16" W, 16" Dp.	13.75"	See LED chart
PCHE1620C	12.5" H, 20" W, 20" Dp.	18"	See LED chart
PCJL2820C	14.5" H*, 20" W, 20" Dp.	5"	3-100W Med. Base or 23W CFL + Crystal Ring – See LED chart

Fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Ella

FINISH: Polished Chrome



AMBER GLASS
& CRYSTAL
DROPS

PCEL1616C DAMP

PCEL1623C DAMP

PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION

DAMP **PCSP2823C**

Superior

FINISH: Polished Chrome

DAMP **PCSP1718C**



BEVELED
CRYSTAL
RODS



PRODUCT	DIMENSIONS	CANOPY	BULBS
PCEL1616C	14" H, 16.5" W, 16.5" Dp.	14"	9-20W Clear G4 XENON Supplied
PCEL1623C	18" H, 23" W, 23" Dp.	19.5"	18-20W Clear G4 XENON Supplied
PCSP1718C	15.5" H, 18" W, 18" Dp.	5"	4-40W Clear G9 XENON Supplied
PCSP2823C	23.5" H*, 23" W, 23" Dp.	6"	6-40W Clear G9 XENON Supplied

Fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.



VLA1618C

INTRICATE
CRYSTAL
DETAIL

Valla

FINISH: Polished Chrome



VLA2820C

PRODUCT	DIMENSIONS	CANOPY	BULBS
VLA1618C	7.5" H, 18.5" W, 18.5" Dp.	13.75"	9-20W Clear G4 XENON Supplied
VLA2820C	10" H*, 20" W, 20" Dp.	1" x 4.75"	6-40W Clear G9 XENON Supplied

*Fixtures comes with 10' of wire.

Ribbons COLLECTION

FINISH:

Crystal Chrome

PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION

RBN2831CRC DAMP

RBN2817CRC DAMP



DAMP **RBN2823CRC**



*All Ribbons pendants (all finishes)
convert to Semi-Flush Mounts*

*Playful swirls
and crystal
accents make
Ribbons an
elegant must
for the
distinguished
home décor.*



detail



RBN1512CRC DAMP



RBN1616CRC DAMP



RBN1622CRC DAMP



RBN1628CRC DAMP



*R*ibbons COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RBN1512CRC	12" H, 12" W, 12" Dp.	1.5"	3-50W Clear G9 Xenon Supplied
RBN1616CRC	9.5" H, 18.5" W, 18.5" Dp.	4.75"	4-40W Clear G9 Xenon Supplied
RBN1622CRC	11" H, 22" W, 22" Dp.	5.75"	5-40W Clear G9 Xenon Supplied
RBN1628CRC	16" H, 27.5" W, 27.5" Dp.	8"	6-40W Clear G9 Xenon Supplied
RBN2817CRC	17" H, 17" W, 17" Dp.	4.75" x 1"	5-40W Clear G9 Xenon Supplied
RBN2823CRC	23" H, 23" W, 23" Dp.	4.75" x 1"	12-40W Clear G9 Xenon Supplied
RBN2831CRC	31" H, 31" W, 31" Dp.	4.75" x 1"	12-40W Clear G9 Xenon Supplied

Cable-hung fixtures come with 8' of wire.

Ribbons COLLECTION

FINISHES:

- C** Polished Chrome
- MN** Millenia
- SG** Satin Copper
- W** White Lustre
- WT** Western Bronze

*All Ribbons pendants
(all finishes) convert to
Semi-Flush Mounts*



detail

PLATINUM
by QUOIZEL


RBN2831WT DAMP





RBN1512SG

RBN2817W



RBN1616WT



RBN2823MN



RBN1622MN



RBN1628W



Ribbons COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RBN1512C/MN/SG/W/WT	12" H, 12" W, 12" Dp.	1.5"	3-50W Frosted G9 Xenon Supplied
RBN1616C/MN/SG/W/WT	8" H, 16.5" W, 16.5" Dp.	4.75"	4-40W Frosted G9 Xenon Supplied
RBN1622C/MN/SG/W/WT	11" H, 22" W, 22" Dp.	5.75"	5-40W Frosted G9 Xenon Supplied
RBN1628C/MN/SG/W/WT	16" H, 27.5" W, 27.5" Dp.	8"	6-40W Frosted G9 Xenon Supplied
RBN2817C/MN/SG/W/WT	17" H, 17" W, 17" Dp.	4.75" x 1"	5-40W Frosted G9 Xenon Supplied
RBN2823C/MN/SG/W/WT	23" H, 23" W, 23" Dp.	4.75" x 1"	12-40W Frosted G9 Xenon Supplied
RBN2831C/MN/SG/W/WT	31" H, 31" W, 31" Dp.	4.75" x 1"	12-40W Frosted G9 Xenon Supplied

Cable-hung fixtures come with 8' of wire.

PCAE1715C

Enlarged for detail

NEW!

FOR 2016



PCAE2820C

Abode

FINISH: Polished Chrome

SHADE: outer: Laser-Cut Metal
inner: Clear organza with Grey Trim

PLATINUM
by QUOIZEL



PCAY1722C

Array

FINISH: Polished Chrome

GLASS: etched



PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
PCAE1715C	9.5" H, 15" W, 15" Dp.	4.75"	3-100W Med. Base or 23W CFL	-
PCAE2820C	18" H*, 20" W, 20" Dp.	5"	3-100W Med. Base or 23W CFL	15.5" x 5.5"
PCAY1722C	9" H, 22" W, 22" Dp.	1" x 4.75"	3-60W Cand. Base	-

Fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.



*As seen in Better Homes & Gardens
LIGHTING Magazine*

PLATINUM MERCURY PENDANT: PCMY2818C (p.181)

Stellar

FINISH: Polished Chrome

GLASS: etched, Painted White inside



DAMP PCSL1616C

PLATINUM
by QUOIZEL

Encompass

FINISH: Millenia

GLASS: o pal

DAMP PCEC1820MN



NEW!

FOR ♦ 2016

METAL
OUTER
SHADE

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCEC1820MN	24.5" H*, 20" W, 20" Dp.	1" x 4.75"	1-100W Med. Base or 23W CFL
PCSL1616C	4.5" H, 16" W, 16" Dp.	-	3-60W Med. Base or 13W CFL

Fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.


BATH COLLECTIONS

Paragon COLLECTION

FINISH:
Polished Chrome

See matching flush mount **PRN1614C** on page 182.

CRYSTAL STRANDS



PRN8606C

Enlarged for detail



PRN8604C

PRN8608C



Paragon COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PRN8604C	4.5" H, 14.5" W, 4" Ext.	7" x 5"	2.5"	4-20W Clear G4 Xenon Supplied
PRN8606C	5" H, 21.5" W, 4" Ext.	7" x 5"	2.5"	6-20W Clear G4 Xenon Supplied
PRN8608C	5" H, 28.5" W, 4" Ext.	7" x 5"	2.5"	8-20W Clear G4 Xenon Supplied

ShimmerCOLLECTION

FINISH:
Polished Chrome

GLASS:
Crystal Studded

DAMP PCSR8603CLED

Enlarged for detail



See matching semi-flush
PCSR1716C on page 181.

PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION

MOUNTS



DAMP PCSR8602CLED

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP PCSR8604CLED



ShimmerCOLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSR8602CLED	8" H, 13.5" W, 5.5" Ext.	4.75" x 4.75"	6"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSR8603CLED	8" H, 23" W, 5.5" Ext.	4.75" x 4.75"	6"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSR8604CLED	8" H, 32" W, 5.5" Ext.	4.75" x 4.75"	6"	4-4.5W Frosted G9 LED Dimmable Supplied

Shimmer bath fixtures can be mounted as uplights or downlights.

Alexa

FINISH: Polished Chrome
GLASS: Crystal

See matching semi-flush
PCAX1714C on page 179.



PCAX8603CLED DAMP

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes



DAMP **PCAX8604CLED**



PCED8517C DAMP

Enlarged for detail

INTEGRATED LED
10 YEAR WARRANTY

MOUNTS

DAMP **PCED8528C**

Endless

FINISH: Polished Chrome
GLASS: optic, Sandblasted inside



DAMP **PCED8521C**

LED CHART

	PCED8517	PCED8521	PCED8528
Lumens	1200	1800	2500
Total Watts	12W	18W	25W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3000K	3000K	3000K
Dimmable	Yes	Yes	Yes

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS/LIGHT SOURCE
PCAX8603CLED	5" H, 25" W, 4" Ext.	24.37" x 5.12"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
PCAX8604CLED	5" H, 33" W, 4" Ext.	32.25" x 5.12"	3"	4-4.5W Frosted G9 LED Dimmable Supplied
PCED8517C	4.5" H, 17.5" W, 4.5" Ext.	17.37" x 4.37"	2.18"	See LED chart
PCED8521C	4.5" H, 21.5" W, 4.5" Ext.	21.25" x 4.37"	2.18"	See LED chart
PCED8528C	4.5" H, 29" W, 4.5" Ext.	28.75" x 4.37"	2.18"	See LED chart



PLATINUM VISION PENDANT:
PCVN2820C (p. 182)

Evermore COLLECTION

PLATINUM

FINISH: Polished Chrome

SHADE: Crystal

EME8604C

Enlarged for detail



PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

FACETED
CRYSTALS



EME8606C



EME8608C

Evermore COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
EME8604C	5" H, 16" W, 6" Ext.	7" x 4.5"	2.5"	4-20W Clear G4 Xenon Supplied
EME8606C	5" H, 23.5" W, 6" Ext.	7" x 4.5"	2.5"	6-20W Clear G4 Xenon Supplied
EME8608C	5" H, 31" W, 6" Ext.	7" x 4.5"	2.5"	8-20W Clear G4 Xenon Supplied

Pierre

FINISH: Brushed nickel
GLASS: optic

INTEGRATED LED

10 YEAR WARRANTY



DAMP PCPR8522BN

Enlarged for detail

LED CHART

	PCPR8522	PCPR8530
Lumens	1800	2200
Total Watts	20W	28W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes



DAMP PCPR8530BN

PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

FACETED
CRYSTALS



DAMP RYE8604C

Enlarged for detail

DAMP RYE8605C

Royale

FINISH: Polished Chrome



PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS/LIGHT SOURCE
PCPR8522BN	4.5" H, 22" W, 4" Ext.	4.5" x 7"	2.5"	See LED chart
PCPR8530BN	4.5" H, 30" W, 4" Ext.	4.5" x 7"	2.5"	See LED chart
RYE8604C	5" H, 20" W, 5" Ext	7" x 4.5"	2.5"	4-20W Clear G4 Xenon Supplied
RYE8605C	5" H, 24" W, 5" Ext	7" x 4.5"	2.5"	5-20W Clear G4 Xenon Supplied

Seaview COLLECTION

PLATINUM

NEW!

FOR ♦ 2016

FINISH: **BN** Brushed nickel **C** Polished Chrome

GLASS: **BN** Clear Thick **C** Clear Thick etched inside



DAMP PCSW8602CLED

Enlarged for detail

MOUNTS

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes



DAMP PCSW8601BNLED

PLATINUM
by QUOIZEL



DAMP PCSW8603BNLED



DAMP PCSW8604CLED

Seaview COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSW8601BNLED / CLED	7" H, 5.5" W, 4.5" Ext.	4.75" x 7"	4"	1-4.5W Frosted G9 LED Dimmable Supplied
PCSW8602BNLED / CLED	5.5" H, 14.5" W, 5" Ext.	7" x 4.75"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSW8603BNLED / CLED	5.5" H, 22" W, 5" Ext.	7" x 4.75"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSW8604BNLED / CLED	5.5" H, 30" W, 5" Ext.	7" x 4.75"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Seaview bath fixtures can be mounted as uplights or downlights.

Serena COLLECTION

NEW!

FOR ♦ 2016

FINISH: Brushed nickel

GLASS: Clear

DAMP PCSA8602BNLED

Enlarged for detail



MOUNTS



DAMP PCSA8603BNLED

PLATINUM
by QUOIZEL

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes



DAMP PCSA8604BNLED

Serena COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSA8602BNLED	6.5" H, 12.5" W, 5.5" Ext.	6.75" x 4.75"	5.12"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSA8603BNLED	6.5" H, 20" W, 5.5" Ext.	6.75" x 4.75"	5.12"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSA8604BNLED	6.5" H, 28" W, 5.5" Ext.	6.75" x 4.75"	5.12"	4-4.5W Frosted G9 LED Dimmable Supplied

Serena bath fixtures can be mounted as uplights or downlights.

Lacombe

FINISH: Polished Chrome
SHADE: Metal Frame with Clear Glass Beads

NEW!
FOR ♦ 2016

PLATINUM


PCLC8603CLED

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS



PCLC8605CLED

PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION



PCMR8603CLED

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

Mirabella

FINISH: Polished Chrome
GLASS: Crystal Accents

NEW!
FOR ♦ 2016

PCMR8605CLED



PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCLC8603CLED	5" H, 18" W, 5.5" Ext.	14.5" x 4.75"	2.5"	3-4.5W Frosted G9 LED Dimmable Supplied
PCLC8605CLED	5" H, 26" W, 6.5" Ext.	19.5" x 4.75"	2.5"	5-4.5W Frosted G9 LED Dimmable Supplied
PCMR8603CLED	9.5" H, 12" W, 5.5" Ext.	12" x 6"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
PCMR8605CLED	11" H, 24" W, 6" Ext.	24" x 6"	3"	5-4.5W Frosted G9 LED Dimmable Supplied

Lacombe and Mirabella bath fixtures can be mounted as uplights or downlights.

Divine COLLECTION

FINISH: Polished Chrome

GLASS: Clear Crystal

DAMP PCDV8602CLED



detail

NEW!

FOR ♦ 2016

MOUNTS

PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes



DAMP PCDV8603CLED

DAMP PCDV8604CLED



Divine COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCDV8602CLED	6" H, 13.5" W, 6" Ext.	7" x 4.75"	5.25"	2-4.5W Frosted G9 LED Dimmable Supplied
PCDV8603CLED	6" H, 23" W, 6" Ext.	7.5" x 4.75"	5.25"	3-4.5W Frosted G9 LED Dimmable Supplied
PCDV8604CLED	6" H, 31.5" W, 6" Ext.	7.5" x 4.75"	5.25"	4-4.5W Frosted G9 LED Dimmable Supplied

Divine bath fixtures can be mounted as uplights or downlights.

DAMP PCDH8522BN



DAMP PCDH8530BN

Dash

FINISH: Brushed nickel
GLASS: White

LED CHART

	PCDH8522BN	PCDH8530BN
Lumens	1600	2240
Total Watts	20W	28W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

INTEGRATED LED
10 YEAR WARRANTY

MOUNTS



Glacial

FINISH: Brushed nickel
GLASS: Clear with Sandblast inside

LED CHART

	PCGL8522BN	PCGL8530BN
Lumens	1700	3200
Total Watts	22W	30W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Dimmable	Yes	Yes

MOUNTS

DAMP PCGL8522BN

Enlarged for detail



DAMP PCGL8530BN

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCDH8522BN	4.5" H, 22" W, 3.5" Ext.	21.5" x 4.5"	2.5"	See LED chart
PCDH8530BN	4.5" H, 30" W, 3.5" Ext.	29.5" x 4.5"	2.5"	See LED chart
PCGL8522BN	5" H, 22" W, 5" Ext.	6" x 5"	2.5"	See LED chart
PCGL8530BN	5.5" H, 30" W, 5" Ext.	6.75" x 5.5"	2.5"	See LED chart

Valiant


NEW!
FOR ♦ 2016

FINISH: Brushed Nickel
GLASS: Clear Etched Inside

PCVT8518BN

Enlarged for detail

MOUNTS



PCVT8524BN

LED CHART

	PCVT8518BN	PCVT8524BN
Lumens	1565	2020
Total Watts	21W	39W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

PLATINUM

by QUOIZEL

INTEGRATED LED

10 YEAR WARRANTY

NEW!
FOR ♦ 2016

Blade

FINISH: Polished Chrome
GLASS: Opal Etched



PCBD8519C

MOUNTS



LED CHART

	PCBD8526C	PCBD8519C
Lumens	2565	1830
Total Watts	33W	25W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	2700K	2700K
Dimmable	Yes	Yes

PCBD8526C

Enlarged for detail

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCBD8519C	5" H, 19" W, 4.5" Ext.	4.75" x 6.75"	2.5"	See LED chart
PCBD8526C	5" H, 26" W, 4.5" Ext.	4.75" x 6.75"	2.5"	See LED chart
PCVT8518BN	5" H, 18" W, 3.5" Ext.	4.5" x 5.75"	2.5"	See LED chart
PCVT8524BN	5" H, 24" W, 3.5" Ext.	4.5" x 5.75"	2.5"	See LED chart

Valiant and Blade bath fixtures can be mounted as horizontally or vertically.



*P*ace

FINISH: Polished Chrome
GLASS: Opal Etched Inner, Clear Outer

PCPC8527C 

Enlarged for detail




 PCPC8533C

LED CHART

	PCPC8527C	PCPC8533C
Lumens	2060	2740
Total Watts	32W	42W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes



INTEGRATED LED
 10 YEAR WARRANTY



*P*romenade

FINISH: Polished Chrome
GLASS: Acrylic Rectangular

PCPE8524C 

Enlarged for detail



LED CHART

	PCPE8524C	PCPE8536C
Lumens	960	1440
Total Watts	8W	12W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes



PCPE8536C 

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCPC8527C	4.5" H, 26.5" W, 4" Ext.	7" x 4.5"	2.5"	See LED chart
PCPC8533C	4.5" H, 33" W, 4" Ext.	7" x 4.5"	2.5"	See LED chart
PCPE8524C	4.5" H, 24" W, 3" Ext.	7" x 4.5"	2.5"	See LED chart
PCPE8536C	4.5" H, 37" W, 3" Ext.	7" x 4.5"	2.5"	See LED chart


BramCOLLECTION

NEW!

FOR ♦ 2016

FINISH: Polished Chrome

GLASS: opal etched



PCBM8520C DAMP

Enlarged for detail


PLATINUM
by QUOIZEL

INTEGRATED LED

10 YEAR WARRANTY



PCBM8505C DAMP



PCBM8526C DAMP

OPTIC GLASS

LED CHART

	PCBM8505C	PCBM8520C	PCBM8526C
Lumens	880	2138	2996
Total Watts	12W	25.5W	36W
Color Rendering Index (CRI)	90	90	90
Color Temperature (CCT)	2700K	3000K	3000K
Dimmable	Yes	Yes	Yes

BramCOLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCBM8505C	13.5" H, 5.5" W, 3.5" Ext.	4.5" x 4.5"	8.75"	See LED chart
PCBM8520C	5.5" H, 20.5" W, 3.5" Ext.	4.5" x 4.5"	3"	See LED chart
PCBM8526C	5.5" H, 26.5" W, 3.5" Ext.	4.5" x 4.5"	3"	See LED chart

Bram bath fixtures can be mounted as horizontally or vertically.

Designer show WCAse

Carolyn Kinder

QUOIZEL



For nearly four decades, **Carolyn Kinder** has been designing and developing innovative collections for the home furnishings industry. Carolyn has an established reputation that has become synonymous with class and timeless design.

With roots in the heartland of America, Kinder travels the globe, discovering and developing sources to deliver rich textures, layered finishes and unique raw materials.

Scan with your smart phone or tablet to view an informative video relating to the Carolyn Kinder Collection by Quoizel!



From the **CAROLYN KINDER CONFETTI COLLECTION: CKCF28220S** (p. 209)
Photo courtesy of Kenorah Design & Build Ltd.

Confetti COLLECTION

FINISH:

OS old silver **RK** rustic Black **NEW!**

SHADE:

inner: off-White Linen
outer: Metal Confetti



DAMP CKCF339RK

CKCF6330OS **DAMP**



NEW!
FOR ♦ 2016

Carolyn Kinder
INTERNATIONAL

DAMP CKCF2825OS



CKCF43624OS

NEW!
FOR ♦ 2016



CKCF2822RK **DAMP**



CKCF1717RK 

NEW!
FOR ♦ 2016



 CKCF1720OS



 CKCF1714OS

NEW!
FOR ♦ 2016



CKCF1508RK 

Carolyn Kinder
INTERNATIONAL



NEW!
FOR ♦ 2016

 CKCF2816RK

Confetti COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
CKCF1508OS/RK	9" H*, 8" W, 8" Dp.	5.5"	1-100W Med. Base or 23W CFL	-
CKCF1714OS	11.5" H, 14" W, 14" Dp.	5.5"	2-100W Med. Base or 23W CFL	5.5" x 13" x 13"
CKCF1717OS/RK	11.5" H, 17" W, 17" Dp.	5.5"	3-100W Med. Base or 23W CFL	5.5" x 16" x 16"
CKCF1720OS	11.5" H, 20" W, 20" Dp.	5.5"	4-100W Med. Base or 23W CFL	5.5" x 19" x 19"
CKCF2816OS/RK	10" H*, 16" W, 16" Dp.	5.5"	3-100W Med. Base or 23W CFL	-
CKCF2822OS/RK	10.5" H*, 22" W, 22" Dp.	5.5"	4-100W Med. Base or 23W CFL	-
CKCF2825OS/RK	10" H*, 25" W, 25" Dp.	5.5"	5-100W Med. Base or 23W CFL	9.5" x 24" x 24"
CKCF3390S/RK	9" H**, 39.5" W, 8" Dp.	.75" x 4.5"	3-100W Med. Base or 23W CFL	-
CKCF43624OS	35" H, 24" W, 1" Dp.	-	-	-
CKCF63300S	29.5" H, 8" W, 14" Dp.	-	2-75W Med. Base or 18W CFL	Fabric Inner Shade: (8.5" x 13") x (7" x 13") x 7" Metal Outer Shade: (8"x14") x (8"x14") x 9"

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
**Comes with (6) 6" and (6) 12" Rods.

Metro COLLECTION

FINISH:

Brushed nickel

SHADE:

Khaki Linen with silver Liner



CKMO2820BN

Carolyn Kinder
INTERNATIONAL



CKMO1716BN



CKMO5003BN



INNER OPAL
ETCHED GLASS

Metro COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.	GLASS
CKMO1716BN	11" H, 15.5" W, 15.5" Dp.	6"	2-60W Med. Base or 13W CFL	15.5" x 6"	-
CKMO2820BN	8" H*, 20" W, 20" Dp.	6"	3-100W Med. Base or 23W CFL	20" x 7"	-
CKMO5003BN	33" H, 33.5" W, 33.5" Dp.	6"	3-100W Med. Base or 23W CFL	Outer: 10" x 6.5"	Opal Etched

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixture comes with 8' of wire. *Comes with 2 (6)" and (2) 12" Rods.

Designer



From the **CAROLYN KINDER**
METRO COLLECTION:
CKM05003BN



CKBT1863T

Sanctuary

FINISH: Driftwood
GLASS: Clear Seedy

NEW!
FOR 2016

Brookmont

with a Hardback Fabric Shade



CKSC5201DR **DAMP**

QUOIZEL
NATURALS
WOOD

Hickman

with a Linen Fabric Shade
with Self Trim top and Bottom

Carolyn Kinder
INTERNATIONAL



CKHM1879T



Ultra
Beveled Mirror

CKUT1921



PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE
CKBT1863T	27" H, 18" W, 9" Dp.	-	1-150W Med. Base (3-way) or 40W CFL	(9" x 18") x (9" x 18") x 9"
CKHM1879T	34" H, 16" W, 16" Dp.	-	2-60W Med. Base or 13W CFL	6" x 16" x 16"
CKSC5201DR	30" H, 18.5" W, 18.5" Dp.	5.5"	1-100W Med. Base or 23W CFL	-
CKUT1921	36" H, 24" W, 2" Dp.	-	-	-

Chain-hung fixture comes with 8' of wire and 4' of chain.

Marisol COLLECTION

Designer

FINISH:
t eco Marrone

SHADE:
inner: Beige hardback Linen
outer: open strap Metal

  **CKMS2822TM**



Carolyn Kinder
INTERNATIONAL



  **CKMS1716TM**

CKMS442TM  

Marisol COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
CKMS1716TM	12" H, 16" W, 16" Dp.	6" x 0.75"	3-100W Med. Base or 23W CFL	14.5" x 6.5"
CKMS2822TM	30" H, 22" W, 22" Dp.	6"	4-100W Med. Base or 23W CFL	19" x 8"
CKMS442TM	32.5" H, 42" W, 11" Dp.	9.75" x 5"	5-100W Med. Base or 23W CFL	8.5" x 39.5" x 8"

All chain-hung fixtures come with 8' of wire and 4' of chain.



CAROLYN KINDER KENDRICK MINI PENDANTS:
CKKD1509WT

Kendrick

FINISH: Western Bronze
GLASS: Moon haze



NEW!
FOR ♦ 2016

CKKD1509WT DAMP

Nikos

FINISH: Burnished silver



DAMP **CKNK1509BV**



DAMP **CKGN1509MZ**

MIRRORED
MERCURY
GLASS



Sonia

FINISH: Artica

CKSN1507AR DAMP

Gaston

FINISH: Mottled Bronze



Carolyn Kinder
INTERNATIONAL

PRODUCT	DIMENSIONS	CANOPY	BULBS
CKGN1509MZ**	10.5" H, 9" W, 9" Dp.	5.5"	1-100W Med. Base or 23W CFL
CKKD1509WT*	19" H, 9.5" W, 9.5" Dp.	1" x 5.5"	1-100W Med. Base or 23W CFL
CKNK1509BV*	14" H, 9" W, 9" Dp.	5.5"	1-60W Vintage Bulb Supplied†
CKSN1507AR**	10.5" H, 7.5" W, 7.5" Dp.	5.5"	1-100W Med. Base or 23W CFL

*Fixtures come with 8' of cable. **Fixtures come with 10' of cable. †Max Wattage: 100W Med. Base or 23W CFL.

Designer show WCAs e

UPTOWN by Sergio Orozco

QUIZEL



From the **UPTOWN EAST VILLAGE COLLECTION: UPEV8701WT**



New York City is the epicenter of American fashion. The Uptown Collection by Sergio Orozco for Quizel captures the eclectic fashion pulse witnessed on the streets of this energetic city and reinterprets it for homeowners who appreciate designs that are fresh, cutting edge and yet comfortably liveable.

Born and raised in Columbia and educated in Europe, Sergio Orozco has received numerous awards for his lighting designs. Now this Manhattan-based designer brings his global perspective to Quizel's Uptown Collection, a unique design that can enhance an eclectic mix of home styles anywhere in the country.



Scan with your smart phone or tablet to view an informative video relating to the Uptown Collection by Sergio Orozco for Quizel!


UPEV5005WT DAMP



East Village

FINISH: Western Bronze

GLASS: Clear



VINTAGE STYLE
bulb included

DAMP **UPEV8701WT**


Enlarged for detail



PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
UPEV5005WT	20" H*, 26" W, 26" Dp.	6.5"	-	5-40W Vintage Bulb Supplied**
UPEV8701WT	11" H, 6.5" W, 5" Ext	6.5" x 6.5"	8"	1-40W Vintage Bulb Supplied**

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 60W Med. Base or 13W CFL

TheaterRow COLLECTION




FINISH:

IS imperial silver

WT Western Bronze

UPTR1716WT DAMP



UPTR5007WT DAMP



DAMP **UPTR8701IS**

TheaterRow COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
UPTR1716WT	6.5" H, 17.5" W, 17.5" Dp.	6"	-	4-60W Vintage Bulb Supplied†
UPTR5007WT	29" H*, 28" W, 28" Dp.	6.5"	-	6-60W Vintage Bulb + 1-50W MR-16 with GU10 Base Shielded Supplied†
UPTR8701IS/WT	10" H, 10" W, 4" Dp.	5.5" Sq.	6.5"	1-60W Vintage Bulb Supplied†

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

†Max Wattage: 100W Med. Base or 23W CFL.

FINISH: Polished Chrome

GLASS: Beveled

UPRZ53426C



UPRZ43426C

PRODUCT

UPRZ43426C

UPRZ53426C

DIMENSIONS

34" H, 26" W, 2" Dp.

34" H, 26" W, 2" Dp.



From the **UPTOWN CARNEGIE COLLECTION:**
UPCN5006WT

Carnegie COLLECTION



FINISH:

IS imperial silver


WT Western Bronze



UPCN5006IS DAMP



UPCN5008WT DAMP



Carnegie COLLECTION


PRODUCT	DIMENSIONS	CANOPY	BULBS
UPCN5006IS/WT	22.5" H*, 25.5" W, 25.5" Dp.	6.5" x 1"	6-60W Vintage Bulb (Supplied)**
UPCN5008IS/WT	30" H*, 34" W, 34" Dp.	6.5"	8-60W Vintage Bulb (Supplied)**

Rod-hung fixtures come with 8' of wire. *Comes with 2 (6") and (2) 12" Rods. **Max Wattage: 100W Med. Base or 23W CFL

MadisonManor COLLECTION

FINISH: Western Bronze
SHADE: Light Beige Fabric



UPMM8701WT  



  UPMM5005WT

MadisonManor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
UPMM5005WT	25.5" H*, 32" W, 32" Dp.	6.5"	-	5-75W Frosted G9 Halogen Supplied	4" x 7.5" x 8.5"
UPMM8701WT	20" H, 8.5" W, 9" Ext.	6.5" x 6.5"	10.5	1-75W Frosted G9 Halogen Supplied	4" x 8.5" x 7.5"

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Designer



From the **UPTOWN MADISON MANOR COLLECTION**
Hanging Fixture: **UPMM5005WT** Wall Fixture: **UPMM8701WT**



Columbus Circle

FINISH: imperial Silver

GLASS: opal etched

UPCC5006IS 



INGENIOUS
DESIGN MOTIF

Fulton

FINISH: imperial Silver

GLASS: opal etched

  **UPFT1820IS**



PRODUCT	DIMENSIONS	CANOPY	BULBS
UPCC5006IS ^{††}	26" H*, 28" W, 28" Dp.	6.5"	6-75W Frosted G9 Halogen Supplied
UPFT1820IS [†]	10.5" H**, 20" W, 20" Dp.	6"	3-100W Med. Base or 23W CFL

*Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods. † Fixture comes with 10' of wire. †† Fixture comes with 12' of wire.

PennStation COLLECTION



FINISH:
BN Brushed nickel **WT** Western Bronze

GLASS:
 Clear



DAMP UPPS1510WT



DAMP UPPS1713BN



DAMP UPPS2813BN




PennStation COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
UPPS1510BN/WT**	17" H*, 10" W, 10" Dp.	6.5"	1-60W Vintage Bulb Supplied††
UPPS1713BN/WT	10.5" H, 13" W, 13" Dp.	6.5"	1-60W Vintage Bulb Supplied††
UPPS2813BN/WT***	23.5" H*, 13" W, 13" Dp.	6.5"	3-40W T8 Vintage Bulb Supplied†

*Comes with (2) 6" and (2) 12" Rods. **Rod-hung fixtures come with 10' of wire. ***Fixture comes with 12' of wire.
 †Max Wattage: 60W Cand. Base. ††Max Wattage: 100W Med. Base or 23W CFL.

VINTAGE STYLE
bulb included



UPSE8701WT

Enlarged for detail

Seaport

FINISH: Western Bronze



UPHL8701IS

Holita

FINISH: imperial silver
SHADE: Light Beige Fabric

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS	SHADE
UPHL8701IS	50" H, 12" W, 6" Ext.	5" x 8"	14"	1-60W Med. Base or 13W CFL	12.5" x 5.5" x 8"
UPSE8701WT	15" H, 4.5" W, 5" Ext.	6.5" x 6.5"	7"	1-40W T8 Vintage Bulb Supplied*	-

*Max Wattage: 60W Cand. Base

QUOIZEL NATURALS



Scan with your smart phone or tablet to view an informative video relating to Quoizel Naturals products!

From the **KYLE COLLECTION:**
KY6328IB (p.73)

Color in Quoizel Naturals products may vary from images shown because of variations in natural materials.

Laguna COLLECTION

FINISH:

Renaissance Copper

SHADE:

Oyster Mica & Mosaic Tile



*Pendant converts
to Semi-Flush Mount*



  **MC8420CRC**



  **MC842CRC**

QUOIZEL
NATURALS
MICA



  **MC842SRC**



MC842FRC  



  MCLG1616RC



  MCLG1612RC



  MC842TRC
Enlarged for detail

QUOIZEL
NATURALS
MICA

Laguna COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
MC842CRC††	6.5" H*, 16" W, 16" Dp.	5"	3-60W Med. Base or 13W CFL	16" x 6"
MC842FRC	60" H, 16" W, 16" Dp.	-	2-60W Med. Base or 13W CFL	16" x 7.5"
MC842SRC	12" H, 16" W, 16" Dp.	5"	3-60W Med. Base or 13W CFL	16" x 6"
MC842TRC	25" H, 16" W, 16" Dp.	-	2-60W Med. Base or 13W CFL	16" x 7.5"
MC8420CRC†	5.5" H*, 22" W, 22" Dp.	5"	4-60W Med. Base or 13W CFL	22" x 6"
MCLG1612RC	5.5" H, 12" W, 12" Dp.	12"	2-60W Med. Base or 13W CFL	12" x 4"
MCLG1616RC	5.5" H, 16" W, 16" Dp.	16"	3-60W Med. Base or 13W CFL	16" x 4.5"

†Rod-hung fixture comes with 8' of wire. ††Fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.





From the **LAGUNA COLLECTION:**
Mini Pendant: **MC842PRC** Pendants: **MC842CRC**
Photo Courtesy of Devane Design

Laguna COLLECTION

FINISH:

Renaissance Copper

SHADE:

Oyster Mica & Mosaic Tile

MC842PRC



Q4574A

NEW!

FOR ♦ 2016

QUOIZEL
NATURALS
MICA

MCLG337RC



Laguna COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
MC842PRC*	7.5" H*, 6" W, 6" Dp.	5"	1-60W Med. Base or 13W CFL	6" x 8"
MCLG337RC**	21" H**, 37" W, 16" Dp.	7.5" x 4.5"	3-100W Med. Base or 23W CFL	37" x 16" x 8"
Q4574A	76" H, 56.5" W, 16" Dp.	-	1-150W Med. Base or 40W CFL	-

*Rod-hung fixture comes with 10' of wire. **Fixture comes with 12' of wire. *Comes with (2) 6" and (2) 12" Rods. **Comes with (4) 6" and (4) 12" Rods.

NEW!
FOR ♦ 2016



 **MC2042T**

Prism
SHADE: Mica

NEW!
FOR ♦ 2016



 **MCAL9470IB**



 **MC1862TIB**
Enlarged for detail

Alistar
FINISH: imperial Bronze
GLASS: Tiffany & Oyster Mica

QUOIZEL
NATURALS
MICA

PRODUCT	DIMENSIONS	BULBS	
MC1862TIB	23" H, 15" W, 9" Dp.	2-60W Med. Base or 13W CFL	Contains 20 Pieces of Tiffany & Mica
MC2042T	25" H, 15.5" W, 15.5" Dp.	2-60W Med. Base or 13W CFL	-
MCAL9470IB	70" H, 15" W, 9.5" Dp.	2-60W Med. Base or 13W CFL	Contains 20 Pieces of Tiffany & Mica




San Gabriel

FINISH: Valiant Bronze
GLASS: Mica & Tiffany

NX615TVA 

QUOIZEL
NATURALS
MICA

PULL-CHAIN



 **MCCS9470AS**

Cyrus

FINISH: Anniversary Silver
GLASS: Oyster Mica & Tiffany Glass

MCCS6326AS 

 **MCCS9357AS**



PRODUCT

MCCS6326AS

DIMENSIONS

25.5" H, 19.5" W, 19.5" Dp.

BULBS

2-60W Med. Base or 13W CFL

Contains 144 pieces of Oyster Mica & Tiffany Glass

MCCS9357AS

57.5" H, 19.5" W, 19.5" Dp.

2-60W Med. Base or 13W CFL

Contains 144 pieces of Oyster Mica & Tiffany Glass

MCCS9470AS

70" H, 19.5" W, 19.5" Dp.

1-150W Med. Base or 40W CFL

Contains 144 pieces of Oyster Mica & Tiffany Glass

NX615TVA

23.5" H, 14.5" W, 14.5" Dp.

2-60W Med. Base or 13W CFL
+ 17W Cand. Base Supplied

Contains 176 pieces of Mica & Tiffany Glass

Kingsford

FINISH: Teco Marrone
SHADE: Oyster Mica



MCKD2819TM 



 MCKD1715TM

MCKD1505TM 



QUOIZEL
NATURALS
MICA

Morrow

FINISH: Mottled Silver
SHADE: Mica

 MC1910MM



PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
MC1910MM	8.5" H*, 18" W, 18" Dp.	6" x .75"	3-60W Med. Base or 13W CFL	14.5" x 7.5"
MCKD1505TM	9" H*, 7.5" W, 5.5" Dp.	6" x .75"	1-60W Med. Base or 13W CFL	4.5" x 5.5" x 6"
MCKD1715TM	11.5" H, 15" W, 15" Dp.	6" x .75"	3-60W Med. Base or 13W CFL	13" x 15" x 6"
MCKD2819TM	15.5" H*, 19" W, 18" Dp.	6" x .75"	3-60W Med. Base or 13W CFL	15" x 18" x 7"

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Pearce

FINISH: Terra Bronze
GLASS: Amber and Oyster Mica




PER6323TB

NEW!
FOR ♦ 2016



PER1715TB

QUOIZEL
NATURALS
MICA



MC1691TIB

Vega

FINISH: imperial Bronze
GLASS: Oyster Mica

PRODUCT	DIMENSIONS	CANOPY	BULBS
MC1691TIB	26" H, 16" W, 16" Dp.	-	2-60W Med. Base or 13W CFL
PER1715TB	14" H, 15" W, 15" Dp.	6"	2-60W Med. Base or 13W CFL
PER6323TB	23" H, 15" W, 15" Dp.	-	2-60W Med. Base or 13W CFL

MCBF2822WT  



  MCBF1717WT

NEW!
FOR ♦ 2016




Belfair

FINISH: Western Bronze

SHADE: Silver Mica & Tempered Glass Diffuser

QUOIZEL
NATURALS
MICA



 MC120T

Highland

SHADE: Soft Green Mica
with Wicker Overlay

PRODUCT	DIMENSIONS	CANOPY	BULBS
MC120T	25" H, 17.5" W, 17.5" Dp.	-	2-60W Med. Base or 13W CFL
MCBF1717WT	9" H, 17" W, 17" Dp.	5"	4-100W Med. Base or 23W CFL
MCBF2822WT	22" H, 22" W, 22" Dp.	5"	5-100W Med. Base or 23W CFL

All chain-hung fixtures come with 8' of wire and 4' of chain.

MC2134TWT



QUOIZEL
NATURALS
MICA

NEW!
FOR ♦ 2016

*T***artan**

FINISH: Western Bronze
SHADE: Mica

*S***andelier**

FINISH: imperial Bronze
SHADE: Oyster Mica

See matching chandelier
BDR5006IB on page 160.



BDR2820IB DAMP



QUOIZEL
NATURALS
AGATE STONE

AG711TVA

*W***hispering Wood**

FINISH: Valiant Bronze
SHADE: Tiffany & Agate Stone

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE
AG711TVA	25" H, 17" W, 17" Dp.	-	2-75W Med. Base or 18W CFL	Contains 104 Pieces of Tiffany & Agate Stone
BDR2820IB	30" H, 20" W, 20" Dp.	5.5"	3-60W Cand. Base	
MC2134TWT	24.5" H, 16" W, 16" Dp.	-	2-60W Med. Base or 13W CFL	

Chain-hung fixture comes with 8' of wire and 4' of chain.

Fen

FINISH: Mystic Black

SHADE: Rattan



ZE1717K



ZE1617K




ZE2822K

Pendant converts to Semi-Flush Mount



QUOIZEL
NATURALS
RATTAN



PRODUCT	DIMENSIONS	CANOPY	BULBS
ZE1617K	6.5" H, 17" W, 17" Dp.	8.25"	3-60W Med. Base or 13W CFL
ZE1717K	12.5" H, 17" W, 17" Dp.	7"	3-100W Med. Base or 23W CFL
ZE2822K	11.5" H*, 22" W, 22" Dp.	5.25"	4-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Arcadia

FINISH: imperial Bronze
SHADE: Butterscotch Onyx

NEW!
FOR ♦ 2016

QUOIZEL
NATURALS
ONYX



DAMP AI1720IB

AI2824IB **DAMP**



Fephyr

FINISH: Muted Bronze
GLASS: Frosted

INDOOR
OUTDOOR

QUOIZEL
NATURALS
SLATE

CAST
Aluminum



ZP8414MD **WET**

WET ZP8418MD

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
AI1720IB	10.5" H, 20" W, 20" Dp.	5"	-	4-100W Med. Base or 23W CFL
AI2824IB	22.5" H*, 24.5" W, 24.5" Dp.	5"	-	5-100W Med. Base or 23W CFL
ZP8414MD	14" H, 7" W, 5.5" Ext	7" x 14"	4.5"	1-50W T4 Mini Can Supplied
ZP8418MD	18" H, 9" W, 7" Ext	9" x 18"	5.5"	1-50W T4 Mini Can Supplied

All rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Aristocrat

FINISH: Palladian Bronze
SHADE: Pen Shell Mosaic

NEW!
 FOR ♦ 2016

AS2824PN DAMP

DAMP AS2818PN



QUOIZEL
NATURALS
PEN SHELL

DAMP AS1716PN



PRODUCT	DIMENSIONS	CANOPY	BULBS
AS1716PN	11.5" H, 16" W, 16" Dp.	5"	4-60W Cand. Base
AS2818PN*	21" H, 18" W, 18" Dp.	.75" x 5"	6-60W Cand. Base
AS2824PN**	25" H, 24" W, 24" Dp.	.75" x 5"	9-60W Cand. Base

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Fixture comes with 12' of wire and 8' of chain.



From the **POMEZ COLLECTION: TF1507VB**
Photo Courtesy of Advance Cabinetry.
www.advancecabinetry.com



Artisans AT WORK

Pomez COLLECTION

n A T U R A I S

FINISH:

VB Vintage Bronze **BC** Burnt Cinnamon
CN Cinnamon

SHADE:

Agate Stone



TF1507VB DAMP


Enlarged for detail



TF135TBC DAMP



TF6825CN DAMP



TF135FBC DAMP

QUOIZEL
NATURALS
AGATE STONE

Pomez COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
TF135FBC	62" H, 18" W, 18" Dp.	-	3-75W Med. Base or 18W CFL
TF135TBC	29.5" H, 18" W, 18" Dp.	-	3-75W Med. Base or 18W CFL
TF1507VB	9" H*, 7" W, 7" Dp.	5.5"	1-100W Med. Base or 23W CFL
TF6825CN	20.5" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL

Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

Captiva

FINISH: Vintage Bronze

SHADE: Sea Shell



NEW!

FOR ♦ 2016

SSCV6222VB 



 SSCV6224VB

QUOIZEL
NATURALS
SEA SHELL

NEW!

FOR ♦ 2016



SSFT6221VB 

Floret

FINISH: Vintage Bronze

SHADE: Sea Shell

the seashell



COLLECTION

beautifully handcrafted from
genuine seashell material

PRODUCT

SSCV6222VB

DIMENSIONS

22.5" H, 12.5" W, 12.5" Dp.

BULBS

2-60W Med. Base or 13W CFL

SHADE

Contains 216 Pieces of Sea Shell

SSCV6224VB

24" H, 16.5" W, 16.5" Dp.

2-75W Med. Base or 18W CFL

Contains 265 Pieces of Sea Shell

SSFT6221VB

21.5" H, 12.5" W, 12.5" Dp.

1-75W Med. Base or 18W CFL

Contains 156 Pieces of Sea Shell

Sanibel

FINISH: Vintage Bronze
SHADE: Sea Shell



NEW!
FOR ♦ 2016



SSSB6223VB 

SSSB1714VB 

QUOIZEL
NATURALS
SEA SHELL

NEW!
FOR ♦ 2016



 JD2077TVB

FlowerField

FINISH: Vintage Bronze
SHADE: Jade

QUOIZEL
NATURALS
JADE

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE
JD2077TVB	25" H, 15.5" W, 15.5" Dp.	-	2-75W Med. Base or 18W CFL	Contains 264 Pieces of Jade
SSSB1714VB	15" H, 14" W, 14" Dp.	5"	2-60W Med. Base or 13W CFL	Contains 252 Pieces of Sea Shell
SSSB6223VB	23" H, 16" W, 16" Dp.	-	2-60W Med. Base or 13W CFL	Contains 181 Pieces of Sea Shell



KendraCOLLECTION

Finish: Mottled Silver **Shade:** Oyster Mica

*For larger images and all product specifications, please see **The Kendra Collection** as it is represented in the Collections Section on pages 64-67.*



KD5015MM



KD5009MM



KD5005MM



KD2824MM



KD2816MM



KD1507MM




KD1716MM

QUOIZEL
NATURALS
MICA



KD8701MM



KyleCOLLECTION

n A T U R A I S

IB Finish: Imperial Bronze **Shade:** Butterscotch Onyx
IN Finish: Iron Gate **Shade:** White Onyx

*For larger images and all product specifications, please see **The Kyle Collection** as it is represented in the Collections Section on pages 68-73.*



KY5016IB




KY5009IB/IN



KY5006IN/IB



KY5506IB



KY1404IB



KY8701IN/IB



KY6328IB



KY540IB/IN



KY433IB



KY5106IB



KY5503IB



KY5103IN/IB



KY2822IB



KY1507IN/IB



KY1508IB/IN



KY8801IB/IN



KY1716IB

QUOIZEL
NATURALS
ONYX

MontereyMosaicCOLLECTION



Finish: Malaga Shade: Pen Shell Mosaic

For larger images and all product specifications, please see **The Monterey Mosaic Collection** as it is represented in the Collections Section on pages 81-86.



MY5005ML



MY5103ML



MY2824ML



MY2816ML



MY1723ML



MY1718ML



MY1613ML



MY1618ML



MY1404ML



MY8801ML



MY1506ML

QUOIZEL
NATURALS
PEN SHELL



MY430242ML



MY430241ML

QUOIZEL
NATURALS

Please see referenced page numbers for larger images and full descriptions of these products.



Chamber

CHB5208DK

See page 106



Chamber

CHB5206DK

See page 106



Chamber

CHB5204DK

See page 106



Chamber

CHB1612DK

See page 106



Armelle

AME5018IB

See page 108



Armelle

AME5009IB

See page 109



Armelle

AME5005IB

See page 109



Armelle

AME8701IB

See page 109



Baron

BRO5204MK

See page 110

QUOIZEL NATURALS

Please see referenced page numbers for larger images and full descriptions of these products.



Baron

BRO5203MK

See page 110



Baron

BRO1715MK

See page 110



Castile

CS5012RK

See page 111



Castile

CS5006RK

See page 111



Castile

CS1718RK

See page 111



Tavern

TVN232DK

See page 120



Tavern

TVN5005DK

See page 120



Tavern

TVN1717DK

See page 120



Odell

ODL5009IB

See page 124



Odell
ODL5005IB
See page 125



Odell
ODL5303IB
See page 125



Odell
ODL2820IB
See page 125



Odell
ODL5206IB
See page 125



Auburn
ABN5024RK
See page 142



Auburn
ABN5012RK
See page 144



Auburn
ABN5006RK
See page 144



Belhaven
BHN5009VG
See page 157



Belhaven
BHN5006VG
See page 157



Belhaven
BHN5303VG
See page 157



Bandelier
BDR5006IB
See page 160



Wyndmoor
WDM5005WT
See page 160

QUOIZEL NATURALS


Please see referenced page numbers for larger images and full descriptions of these products.



Holbrook

HK5008TC

See page 166



Holbrook

HK5005TC

See page 166



Planter

QF1840RK

See page 166



Kayden

KDN5004BN

See page 169



Pembroke

PB5008TK

See page 170



Pembroke

PB5004TK

See page 170



Anchor

ANR5010IB

See page 171



Anchor

ANR5006IB

See page 171



Kayden

KDN1510BN

See page 280

Island lights

QUOIZEL



From the **DELUXE COLLECTION: DX348C** (p.261)
Photo Courtesy of Natalie Howe Design.

Alexandria

FINISH: Palladian Bronze



See matching Alexandria styles on p. 104

DANGLING GLASS ACCENTS


Brook Hall

FINISH: Western Bronze

See matching Brook Hall styles starting on p. 42

BKH838WT

NEW!
FOR ♦ 2016



AX434PN

Laguna

FINISH: Renaissance Copper
SHADE: Oyster Mica & Mosaic tile

See matching Laguna styles starting on p. 228

QUOIZEL
NATURALS
MICA

MCLG337RC



PRODUCT	DIMENSIONS	CANOPY	BULBS
AX434PN†	8" H*, 15.5" W, 33.5" Dp.	4.5"	4-100W Med. Base or 23W CFL
BKH838WT	15.5" H, 38" W, 12" Dp.	9" x 4.75"	8-60W Cand. Base
MCLG337RC††	21" H*, 37" W, 16" Dp.	7.5" x 4.5"	3-100W Med. Base or 23W CFL

Chain-hung fixture comes with 8' of wire and 4' of chain. †Rod-hung fixture comes with 8' of wire.
††Rod-hung fixture comes with 12' of wire. *Comes with (4) 6" and (4) 12" Rods.

DAMP ADS639DC

Adonis

FINISH: d ark Cherry

GLASS: Opal Etched and Clear Water

See matching Adonis styles starting on p. 38



Emery

FINISH: **BN** Brushed n ickel

IS imperial silver

PN Palladian Bronze

SHADE: Metal

ER353BN



See matching Emery styles starting on p. 61

ER353 is available in THREE finishes!

IS



PN



PRODUCT

ADS639DC††

ER353BN/IS/PN†

DIMENSIONS

19" H*, 39" W, 19.5" Dp.

23.5" H*, 52.5" W, 13" Dp.

CANOPY

8" x 4.5"

9" x 4.5"

BULBS

6-60W Cand. Base

3-100W Med. Base or 23W CFL

†Rod-hung fixture comes with 8' of wire. ††Fixture comes with 10' of wire. *Comes with (4) 6" and (4) 12" Rods.

Tavern


FINISH: Dark Bronze

See matching Tavern styles on p. 120

TVN232DK



QUOIZEL
**NATURALS
WOOD**




See matching New Harbor styles on p. 133

Eastvale

FINISH: Palladian Bronze
SHADE: Metal with Clear Ribbed Glass Diffuser

See matching Eastvale styles on p. 105

EVE240PN



CLEAR RIBBED
DIFFUSER

New Harbor

FINISH: Western Bronze

NHR538WT



PRODUCT	DIMENSIONS	CANOPY	BULBS
EVE240PN	29" H*, 40" W, 14.5" Dp.	6"	2-100W Med. Base or 23W CFL
NHR538WT	9.5" H**, 38" W, 12" Dp.	9" x 4.75" x .75"	5-60W Vintage Bulbs Supplied†
TVN232DK	10.5" H**, 32" W, 12" Dp.	10.5" x 4.5"	6-60W Vintage Bulbs Supplied†

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.
**Comes with (4) 6" and (4) 12" Rods. †Max Wattage: 100W Med. Base or 23W CFL.

island lights



From the **CAROLYN KINDER**
MARISOL COLLECTION:
CKMS442TM

Confetti

FINISH: OS Old silver **RK** Rustic Black **NEW!**

SHADE: Outer: Metal Confetti
inner: Off-White Linen

See matching Confetti
styles starting on page 208

CKCF339RK



CKCF339OS

Caroly Kinder
INTERNATIONAL

CKMS442TM



Marisol

FINISH: teco Marrone

SHADE: Beige hardback Linen

See matching Marisol
styles on page 213

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE
CKCF339OS/RK†	9" H*, 39.5" W, 8" Dp.	.75" x 4.5"	3-100W Med. Base or 23W CFL	-
CKMS442TM††	32.5" H, 42" W, 11" Dp.	5" x 9.75"	5-100W Med. Base or 23W CFL	8.5" x 39.5" x 8"

†Rod-hung fixtures come with 8' of wire. *Comes with (6) 6" and (6) 12" Rods. ††Chain-hung fixture comes with 8' of wire and 4' of chain.

Duchess

FINISH: AN antique nickel PN Palladian Bronze
SHADE: AN grey Marble PN Champagne Marble

DAMP DH348AN



DAMP DH348PN



See matching Duchess styles starting on p. 52

La Parra

FINISH: imperial Bronze
SHADE: Candella scavo

See matching La Parra styles starting on p. 74

DAMP LP639IB



PRODUCT	DIMENSIONS	CANOPY	BULBS
DH348AN/PN	27" H, 48" W, 14" Dp.	6.5"	3-100W Med. Base or 23W CFL
LP639IB	46" H, 38" W, 19" Dp.	7" x 4.5"	6-100W Med. Base or 23W CFL

Chain-hung fixture comes with 8' of wire and 4' of chain.

QUOIZEL
NATURALS
ONYX



KY540IN DAMP


Kyle

- FINISH:** **IB** imperial Bronze
IN iron gate
- SHADE:** **IB** Butterscotch Onyx
IN White Onyx

KY540 is also available in Imperial Bronze



See matching Kyle styles in the starting on on page 68



KY433IB DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
KY433IB	18.5" H, 33" W, 4.5" Dp.	8" x 4.5"	4-100W Med. Base or 23W CFL
KY540IB/IN	23" H, 40" W, 5.5" Dp.	11.75" x 4.75"	5-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

 **DX348C**

Deluxe

FINISH: Polished Chrome
SHADE: Cream Linen hardback

See matching *Deluxe* styles
on pages 290 and 349



CRYSTAL ACCENTS

TY628AN 

Taylor

FINISH: antique nickel
GLASS: Opal Etched

See matching
Taylor styles
starting on p. 87



Remi

FINISH: Polished Chrome
SHADE: White Fabric

See matching
Remi styles
on p. 123



REM345C 

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
DX348C [†]	33" H, 48" W, 12" Dp.	8"	3-150W Med. Base or 40W CFL	10" x 48" x 12"
REM345C ^{††}	10" H, 44.5" W, 5.5" Dp.	18" x 4.5"	3-75W Med. Base or 18W CFL	6" x 10.5" x 5.5"
TY628AN ^{**}	16.5" H*, 28" W, 16" Dp.	9" x 4.75" x 0.875"	6-100W Med. Base or 23W CFL	-

*Comes with (4) 6" and (4) 12" Rods. **Rod-hung fixture comes with 8' of wire.
[†]Chain-hung fixture comes with 8' of wire and 4' of chain. ^{††}Cable-hung fixture comes with 12' of wire.

Asheville

FINISH: Valiant Bronze

See matching Asheville styles starting on page 470

TFAS344VA



Belle Fleur

FINISH: Vintage Bronze

See matching Belle Fleur styles starting on page 483

TFBF348VB

Inglenook

FINISH: Valiant Bronze

See matching Inglenook styles starting on page 464

TFIK348VA



PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TFAS344VA	29" H, 44" W, 19" Dp.	10" x 4.5" x 1"	3-100W Med. Base or 23W CFL	Contains 316 Pieces of Tiffany Glass
TFBF348VB	18" H, 48" W, 16" Dp.	8" x 4.5"	3-100W Med. Base or 23W CFL	Contains 884 Pieces of Tiffany Glass
TFIK348VA	17.5" H, 47.5" W, 16" Dp.	8" x 4.5"	3-100W Med. Base or 23W CFL	Contains 496 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

P

ENDANTS

QUOIZEL



MOROCCO PENDANT:
QF2046C (p. 270)

Orion COLLECTION

FINISH:

BN Brushed Nickel **WT** Western Bronze

GLASS: Clear Accents

NEW!

FOR ♦ 2016

ON2824BN DAMP



detail

DAMP ON2824WT




DAMP ON2818WT



DAMP ON2818BN



Pendants convert to Semi-Flush Mounts



Orion COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ON2818BN/WT	19.5" H*, 18" W, 18" Dp.	5.5"	4-60W Cand. Base
ON2824BN/WT	25.5" H*, 24" W, 24" Dp.	5.5"	6-60W Cand. Base

All rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Jarvis

FINISH: Old Silver

SHADE: Off White Linen Hardback Fabric

JV2820OS



SAND BLASTED
DIFFUSER

NEW!
FOR ♦ 2016

Pendant convert to
Semi-Flush Mount



JV2816OS



Amelia

FINISH: Old Bronze

GLASS: Etched Painted White inside

AML2821OZ



NEW!
FOR ♦ 2016

See matching chandelier
AML5005OZ on page 162.

GLASS
ACCENTS

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
AML2821OZ††	24.5" H, 21" W, 21" Dp.	1.5" x 5.75"	3-100W Med. Base or 23W CFL	-
JV2816OS†	10" H*, 16" W, 16" Dp.	5.5"	3-100W Med. Base or 23W CFL	8" x 14" x 14"
JV2820OS†	10" H*, 20" W, 20" Dp.	5.5"	3-100W Med. Base or 23W CFL	8" x 17" x 17"

*Comes with (2) 6" and (2) 12" Rods. †Rod-hung fixtures come with 8' of wire. ††Chain-hung fixture comes with 8' of wire and 4' of chain.



From the **PORTLAND COLLECTION:**
PTD2826WT
Photo courtesy of LDK Homes

Pendant converts to Semi-Flush Mount



Portland

FINISH: **BN** Brushed Nickel
WT Western Bronze

SHADE: **BN** Clear Organza with Light Grey Trim
WT Light Amber Organza with Bronze Trim



PTD2826BN DAMP

Pendant converts to Semi-Flush Mount



DAMP **PTD2820WT**



DAMP **BWL2816CC**

DAMP **BWL2822CC**



STUDDED FAUX BRASS ACCENTS

See matching Brown Lattice styles on page 280 and 288.

Brown Lattice

FINISH: Copper Canyon
SHADE: Outer: Metal with Studded Faux Brass Accents
Inner: Tan Fabric Hardback



PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
BWL2816CC	10" H*, 16" W, 16" Dp.	5.5"	3-100W Med. Base or 23W CFL	Outer: 16" x 10", Inner: 15" x 9.5"
BWL2822CC	10" H*, 22" W, 22" Dp.	5.5"	4-100W Med. Base or 23W CFL	Outer: 22" x 10", Inner: 21" x 9.5"
PTD2820BN/WT	16.5" H*, 20" W, 20" Dp.	5"	4-60W Cand. Base	20" x 6"
PTD2826BN/WT	24" H*, 28" W, 28" Dp.	5"	8-60W Cand. Base	28" x 8"

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Capri

FINISH: imperial Bronze
SHADE: Beige Linen with Brown Trim

See matching chandelier
CP5006IB on page 160.

DAMP CP2820IB



Pendant converts to Semi-Flush Mount



See matching flush mount
BND1613BA on page 307.

VINTAGE STYLE
 bulb included



DAMP BND1818BA



Sound

FINISH: Royal Ebony

Pendant converts to Semi-Flush Mount



DAMP RLY1815IB

Railway

FINISH: imperial Bronze

See matching mini-pendant
RLY1512IB on page 283.



PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
BND1818BA	7.5" H*, 18" W, 18" Dp.	5.5" x .75"	4-40W T8 Vintage Bulbs Supplied**	-
CP2820IB	14.5" H*, 20" W, 20" Dp.	5"	4-60W Cand. Base	16" x 16" x 7"
RLY1815IB	11" H*, 15.5" W, 15.5" Dp.	6" x .75"	1-100W Med. Base or 23W CFL	-

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 60W Cand. Base.



JLE2812IS DAMP

See matching semi-flush mount **JLE1709IS** on page 296.



Zolene

FINISH: imperial Silver

JLE2809IS DAMP

Mirage

FINISH: Vintage Gold

See matching Mirage styles on page 296.



MIR2818VG DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
JLE2809IS	19" H , 9" W, 9" Dp.	5"	2-60W Cand. Base
JLE2812IS	22" H, 12" W, 12" Dp.	5"	3-60W Cand. Base
MIR2818VG	21.5" H, 18.5" W, 18.5" Dp.	6" x 0.75"	4-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

DAMP  **CDY2814BN**

Cody

FINISH: Brushed Nickel

See matching Cody styles
on page 280 & 297.



VINTAGE STYLE
bulb included



DAMP **QF2046C**

Morocco

FINISH: Polished Chrome

GLASS: Clear Hand Blown

See matching mini pendant
QF2047C on page 279.



HAND BLOWN
GLASS

NEW!
FOR  2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
CDY2814BN ^{††}	10.5" H*, 14.5" W, 14.5" Dp.	5"	2-100W Med. Base or 23W CFL
QF2046C [†]	21.5" H*, 16" W, 16" Dp.	.75 x 5.75"	1-60W Vintage Bulb Supplied**

[†]Cable-hung fixtures come with 8' of wire. ^{††}Rod-hung fixtures come with 12' of wire.

*Comes with (2) 6" and (2) 12" Rods. **Max. Wattage: 100W Med. Base or 23W CFL.

CRA2826MC

Cloverdale

FINISH: Mottled Cocoa
SHADE: Khaki Fabric



See matching semi-flush
CRA1717MC on page 290.

CRA2822MC

Pendant converts
to Semi-Flush Mount



Pendant converts
to Semi-Flush Mount



Long Beach

FINISH: Western Bronze

LBH2820WT



Pendant converts
to Semi-Flush Mount




PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
CRA2822MC	12" H*, 22" W, 22" Dp.	5.5"	4-100W Med. Base or 23W CFL	22" x 10.5"
CRA2826MC	9.5" H*, 26" W, 26" Dp.	6.5"	4-100W Med. Base or 23W CFL	26" x 8"
LBH2820WT	10.5" H*, 20" W, 20" Dp.	6" x 1"	3-60W Vintage Bulb (Supplied)**	-

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 100W Med Base or 23W CFL.


Pendants

Please see referenced page numbers for larger images and full descriptions of these products.



Adonis

ADS2818DC
See page 39



Baroness

BNS2818WT
See page 41



Buchanan

BCN2820WT
See page 45



Downtown

DW1824C
See page 51




Downtown

DW2817C
See page 51



Duchess

DH2820AN/PN
See page 54



Dury

RDY2821PN/CS
See page 60



Dury

RDY2823CS/PN
See page 60



Emery

ER1814BN/IS/PN
See page 62



Kendra

KD2816MM
See page 67






Kendra

KD2824MM
See page 67



Kyle

KY2822IB
See page 72



Pendants

Please see referenced page numbers for larger images and full descriptions of these products.



Odell
ODL28201B
See page 125



Wilder
WLR2820MB
See page 135



PI ATiNUM Co II ECTio N
Bordeaux
BRX2818C
See page 174



PI ATiNUM Co II ECTio N
Galaxy
PCGX1817C
See page 178



PI ATiNUM Co II ECTio N
Galaxy
PCGX1826C
See page 178



PI ATiNUM Co II ECTio N
Arena
PCAN2814C
See page 180



PI ATiNUM Co II ECTio N
Crystal Leaf
PCCF2824C
See page 180



PI ATiNUM Co II ECTio N
Mercury
PCMY2818C
See page 181



PI ATiNUM Co II ECTio N
Vision
PCVN2820C
See page 182



PI ATiNUM Co II ECTio N
Janelle
PCJL2820C
See page 183



PI ATiNUM Co II ECTio N
Superior
PCSP2823C
See page 184



PI ATiNUM Co II ECTio N
Valla
VLA2820C
See page 185

PI ATiNUM Co II ECTio N

Ribbons

RBN2831CRC

See page 186



PI ATiNUM Co II ECTio N

Ribbons

RBN2823CRC

See page 186




PI ATiNUM Co II ECTio N

Ribbons

RBN2817CRC

See page 186




PI ATiNUM Co II ECTio N

Ribbons

RBN2831C/MN/SG/W/WT

See page 188




PI ATiNUM Co II ECTio N

Ribbons

RBN2823C/MN/SG/W/WT

See page 189




PI ATiNUM Co II ECTio N

Ribbons

RBN2817C/MN/SG/W/WT

See page 189



PI ATiNUM Co II ECTio N

Abode

PCAE2820C

See page 190



PI ATiNUM Co II ECTio N

Encompass

PCEC1820MN

See page 192



CARo IYN KiNDER

Confetti

CKCF28220S/RK

See page 208



CARo IYN KiNDER

Confetti

CKCF28250S/RK

See page 208



CARo IYN KiNDER

Confetti

CKCF28160S/RK

See page 209



CARo IYN KiNDER

Metro

CKMO2820BN

See page 210





From the **LAGUNA COLLECTION: MC8420CRC** (p.228)
Photo Courtesy of Devane Designs



CAROLYN KINDER

Marisol

CKMS2822TM

See page 213



UPTOWN
COLLECTION

Fulton

UPFT1820IS

See page 224



UPTOWN
COLLECTION

Penn Station

UPPS2813BN/WT

See page 225



Laguna

MC8420CRC

See page 228



Laguna

MC842CRC

See page 228



Morrow

MC1910MM

See page 235



Kingsford

MCKD2819TM

See page 235



Belfair

MCBF2822WT

See page 237



Bandelier

BDR2820IB

See page 238



Zen

ZE2822K

See page 239



Arcadia

AI2824IB

See page 240



Aristocrat

AS2818PN

See page 241



Aristocrat

AS2824PN

See page 241



*Please see the **Quoizel Tiffany Collection** on page 459 for many attractive art glass pendant lighting solutions.*


MINI PENDANTS | QUOIZEL



From the **TIFFANY HYACINTH COLLECTION:**
TF1536VB (p.487)
Photo courtesy of Enmark Construction Ltd.

MOROCCO

FINISH: Polished Chrome
GLASS: Clear Hand Blown



See matching pendant
QF2046C on page 270.

NEW!
 FOR ♦ 2016

HAND BLOWN
 GLASS



DAMP QF2047C

DAMP QPP2049WT

DAMP QPP2049BN

NEW!
 FOR ♦ 2016

Garrison

FINISH: **BN** Brushed Nickel
WT Western Bronze
GLASS: opal Etched

See matching Garrison
 bath styles on page 351.



PRODUCT	DIMENSIONS	CANOPY	BULBS
QF2047C†	13.5" H, 10" W, 10" Dp.	.75 x 5.75"	1-60W Vintage Bulb Supplied**
QPP2049BN/WT††	7.5" H*, 7.5" W, 7.5" Dp.	5"	1-100W Med. Base or 23W CFL

†Cable-hung fixtures come with 8' of wire. ††Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max. Wattage: 100W Med. Base or 23W CFL.

Brown Lattice

FINISH: Copper Canyon
SHADE: Outer: Metal with Faux Brass Studded Accents
 Inner: Tan Fabric Hardback

CDY1508BN 

See matching Brown Lattice styles on pages 267 and 288.

BWL1508CC 



Cody

FINISH: Brushed Nickel

See matching Cody styles on pages 270 & 297.

Ferndale

FINISH: Western Bronze
GLASS: Outer: Clear Seedy
 Inner: Tiffany Glass

 KDN1510BN

FE1506WT 



QUOIZEL NATURALS WOOD

Kayden

FINISH: Brushed Nickel
GLASS: Clear Seedy

See matching chandelier **KDN5004BN** on page 169.



PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
BWL1508CC [†]	9" H*, 8" W, 8" Dp.	5.5"	1-100W Med. Base or 23W CFL	Outer: 8" x 9", Inner: 7.5" x 8.75"
CDY1508BN**	9" H*, 8" W, 8" Dp.	5"	1-100W Med. Base or 23W CFL	
FE1506WT**	12.5" H*, 6" W, 6" Dp.	6"	1-100W Med. Base or 23W CFL	-
KDN1510BN**	10.5" H*, 10" W, 10" Dp.	5"	1-60W Cand. Base	

*Comes with (2) 6" and (2) 12" Rods. **Rod-hung fixtures come with 8' of wire. †Fixture comes with 10' of wire.

MINI-PENDANTS

INDOOR
OUTDOOR

Steadman

FINISH: imperial Bronze
GLASS: Clear Seedy

See matching Steadman styles on page 436-437.

SDN1506IB DAMP

MRE1506WT DAMP

See matching Marine styles on page 426-427.

Ridley

FINISH: Western Bronze
GLASS: Clear

VINTAGE STYLE
bulb included



Marine

FINISH: Western Bronze

INDOOR
OUTDOOR

CAST
Aluminum

QPP1401WT DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS
MRE1506WT ^{††}	12" H*, 6" W, 6" Dp.	6"	1-60W Vintage Bulb Supplied**
QPP1401WT ^{††}	11" H*, 11.5" W, 11.5" Dp.	6"	1-60W Vintage Bulb Supplied**
SDN1506IB [†]	12" H*, 5.5" W, 5.5" Dp.	6"	1-60W Vintage Bulb Supplied**

*Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 100W Med. Base or 23W CFL. [†]Rod-hung fixture comes with 8' of wire. ^{††}Fixture comes with 10' of wire.

Dublin

FINISH: Brushed Nickel
GLASS: Clear Pressed

See matching Dublin styles on page 345.

DAMP DBN1506BN



DAMP QPP2048BN



Valentina

FINISH: Brushed Nickel
SHADE: Outer: Clear Glass
 Inner: Metal



DAMP QPP2050BN

Antero

FINISH: Brushed Nickel
GLASS: Clear Seedy

NEW!

FOR ♦ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS
DBN1506BN	7.5" H*, 6.5" W, 6.5" Dp.	5"	1-100W Med. Base or 23W CFL
QPP2048BN	13" H*, 6" W, 6" Dp.	1" x 5"	1-100W Med. Base or 23W CFL
QPP2050BN	8" H*, 4.5" W, 4.5" Dp.	4.75"	1-60W Clear G9 Xenon Supplied

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Railway

FINISH: imperial Bronze
SHADE: Metal

See matching pendant
RLY1815IB on page 268.

DAMP RLY1512IB

Mini-Pendant converts
to Semi-Flush Mount



QPP2051IS **DAMP**

Highgate

FINISH: imperial Silver
GLASS: Clear

NEW!
FOR **2016**




PRODUCT	DIMENSIONS	CANOPY	BULBS
QPP2051IS	13.5" H*, 9.5" W, 9.5" Dp.	6"	1-60W Vintage Bulb Supplied**
RLY1512IB	8" H*, 12" W, 12" Dp.	6" x .75"	1-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods. **Max Wattage: 100W Med. Base or 23W CFL.

Mini Pendants

Please see referenced page numbers for larger images and full descriptions of these products.



Adonis

ADS1504DC


See page 39



Baroness

BNS1505WT

See page 40



Downtown

DW1506C/D

See page 51



Duchess

DH1506AN/PN


See page 56



Dury

RDY1506CS

See page 60



Emery

ER1508BN/IS/PN


See page 62



Kendra

KD1507MM

See page 67



Kyle

KY1507IB/IN

See page 73



Kyle

KY1508IB/IN

See page 73



La Parra

LP1505IB

See page 76



Monterey Mosaic

MY1506ML

See page 86



Trilogy

TRG1508OZ

See page 94



Eastvale

EVE1508PN
See page 105



Grant

GRT1508BN/IS/PN
See page 115



Metropolis

MTP1510AN
See page 117



New England

NA1514BN
See page 119



New England

NA1510BN
See page 119



Sophia

SPH1508PN/BN
See page 132



Wilder

WLR1506MB
See page 135




Union Station

UST1505WT
See page 140




PLATINUM Co II ECTio N Treasure

PCTS1503C
See page 181



PLATINUM Co II ECTio N Ribbons

RBN1512CRC
See page 187



PLATINUM Co II ECTio N Ribbons

RBN1512C/MN/SG/W/WT
See page 189



CARo IYN KiNDER Confetti

CKCF1508OS/RK
See page 209

Mini Pendants

Please see referenced page numbers for larger images and full descriptions of these products.





From the
OZARK COLLECTION:
OZ1616IN (p.306)

QUOIZEL



SEMI-FLUSH & FLUSH MOUNTS

Brown Lattice

FINISH: Copper Canyon

SHADE: Outer: Metal Shade with Faux Studded Brass Accents
Inner: Tan Fabric Hardback

See matching Brown Lattice style on page 267 and 280.

 **BWL1717CC**



FAUX BRASS ACCENTS



Surgess

FINISH: Rustic Black
GLASS: Mercury

NEW!
FOR ♦ 2016

BGS1715RK 

See matching chandelier **BGS5203RK** on page 170.

 **FTR1713IB**

Frontier

FINISH: Imperial Bronze

See matching chandelier **FTR5204IB** on page 161.



PRODUCT	DIMENSIONS	CANOPY	BULBS
BGS1715RK	15.5" H, 15" W, 15" Dp.	5"	3-60W Cand. Base
BWL1717CC	11" H, 17" W, 17" Dp.	5.5"	3-100W Med. Base or 23W CFL
FTR1713IB	13" H, 13" W, 13" Dp.	0.75"	3-60W Cand. Base



QF1213SHO DAMP



QF1213SBN DAMP

Norwood

FINISH: **BN** Brushed Nickel
HO Harbor Bronze
GLASS: Opal Etched



CLT1714BN DAMP

Celestial

FINISH: Brushed Nickel
GLASS: Opal Etched

*See matching chandelier
 CLT5004BN on page 162.*

PRODUCT	DIMENSIONS	CANOPY	BULBS
CLT1714BN	15" H, 14" W, 14" Dp.	5"	4-100W Med. Base or 23W CFL
QF1213SBN/SHO	11" H, 19" W, 19" Dp.	6" Sq.	4-100W Med. Base or 23W CFL



Waverly

FINISH: Brushed Nickel
SHADE: White Linen Fabric

WV1716BN 

See matching
 Deluxe styles on
 pages 261 and 349

Deluxe

FINISH: Polished Chrome
SHADE: Cream Linen Hardback

 **DX1718C**



FROSTED
 WHITE
 DIFFUSER

CRYSTAL
 FINIAL

CRA1717MC 



Cloverdale

FINISH: Mottled Cocoa
SHADE: Khaki Fabric

See matching Cloverdale
 styles on page 271.

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
CRA1717MC	12.5" H, 17" W, 17" Dp.	6.5"	3-100W Med. Base or 23W CFL	-
DX1718C	16.5" H, 18" W, 18" Dp.	8"	3-60W Med. Base or 13W CFL	7" x 15.5" x 17.5"
WV1716BN	11.5" H, 16" W, 16" Dp.	6"	3-100W Med. Base or 23W CFL	4" x 14" x 16"

SEMI-FLUSH



From the
DELUXE COLLECTION:
DX1718C
*Photo Courtesy of
Studio M. Interiors*

DAMP SLR1716AN



Sailor

FINISH: AN Antique Nickel
WT Western Bronze
GLASS: Etched

DAMP SLR1720WT



NEW!
FOR ♦ 2016



Calvary

FINISH: Western Bronze
SHADE: Light Beige Fabric Hardback

DAMP QF1715WT

ETCHED GLASS
 DIFFUSER

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
QF1715WT	10.5" H, 17.5" W, 17.5" Dp.	6"	3-100W Med. Base or 23W CFL	15" x 5"
SLR1716AN/WT	9.5" H, 16" W, 16" Dp.	5"	4-100W Med. Base or 23W CFL	
SLR1720AN/WT	9.5" H, 20" W, 20" Dp.	6"	5-100W Med. Base or 23W CFL	

SEMI-FLUSH

Ashland

FINISH: Western Bronze
GLASS: Etched Painted White Inside



QF1202SWT



QF1201SWT



OZ1713IN



OZ1716PN

Ozark

FINISH: **IN** Iron Gate **PN** Palladian Bronze
GLASS: Etched Painted White Inside

See matching Ozark flush mounts on page 306.

PRODUCT	DIMENSIONS	CANOPY	BULBS
OZ1713IN/PN	9.5" H, 13" W, 13" Dp.	5"	2-100W Med. Base or 23W CFL
OZ1716IN/PN	12" H, 16.5" W, 16.5" Dp.	5"	3-100W Med. Base or 23W CFL
QF1201SWT	12" H, 25" W, 25" Dp.	6"	4-100W Med. Base or 23W CFL
QF1202SWT	11" H, 20" W, 20" Dp.	6"	3-100W Med. Base or 23W CFL

Griffin

FINISH: AN Antique Nickel
 PN Palladian Bronze
GLASS: Etched Painted White Inside

See matching Griffin flush mounts on page 305.

GF1721AN DAMP

Enlarged for detail



GF1717AN DAMP



DAMP **GF1721PN**



DAMP **GF1717PN**



PRODUCT

GF1717AN/PN

GF1721AN/PN

DIMENSIONS

12" H, 17" W, 17" Dp.

14" H, 21" W, 21" Dp.

CANOPY

5.75"

5.75"

BULBS

3-100W Med. Base or 23W CFL

4-100W Med. Base or 23W CFL

SEMI-FLUSH



From the **GRIFFIN COLLECTION:**
GF1717PN




Jolene

FINISH: Imperial Silver

DAMP MJY1615VG

JLE1709IS **DAMP**

See matching Jolene styles on page 269.



Majesty

FINISH: Vintage Gold

See matching chandelier **MJY5304VG** on page 159.



MIR1715VG **DAMP**

Mirage

FINISH: Vintage Gold

See matching pendant **MIR2818VG** on page 269.



DAMP **MIR1718VG**

PRODUCT	DIMENSIONS	CANOPY	BULBS
JLE1709IS	13.5" H, 9.5" W, 9.5" Dp.	4.5"	2-60W Cand. Base
MIR1715VG	11.5" H, 15" W, 15" Dp.	6"	3-100W Med. Base or 23W CFL
MIR1718VG	11.5" H, 18.5" W, 18.5" Dp.	6"	4-100W Med. Base or 23W CFL
MJY1615VG	14" H, 15.5" W, 15.5" Dp.	1.25" x 5"	4-60W Cand. Base



Cody

FINISH: Brushed Nickel

See matching Cody styles on pages 270 and 280.

CDY1714BN  



Warren

FINISH: Brushed Nickel

GLASS: Opal Etched

  **QF1678BN**

 **QF1834BN**



Selcourt

FINISH: **BN** Brushed Nickel

WT Western Bronze

GLASS: Etched Painted White Inside

 **QF1831BN**



Castle

FINISH: Brushed Nickel

GLASS: Etched Painted White Inside

PRODUCT	DIMENSIONS	CANOPY	BULBS
CDY1714BN	12" H, 14.5" W, 14.5" Dp.	5"	2-100W Med. Base or 23W CFL
QF1678BN	10" H, 13.5" W, 13.5" Dp.	6.5"	1-100W Med. Base or 23W CFL
QF1831BN	10" H, 17" W, 17" Dp.	6"	4-100W Med. Base or 23W CFL
QF1834BN/WT	11" H, 18" W, 18" Dp.	5"	3-100W Med. Base or 23W CFL

Semi-Flush Mounts

Please see referenced page numbers for larger images and full descriptions of these products.

Baroness

BNS1715WT
See page 41



Brook Hall

BKH1714WT
See page 42



Buchanan

BCN1716WT
See page 45



Downtown

DW1717C/D
See page 51



Duchess

DH1718AN/PN
See page 56



Dury

RDY1714CS/PN
See page 60



Kendra

KD1716MM
See page 67



Kyle

KY1716IB
See page 72



Monterey Mosaic

MY1718ML
See page 85



Monterey Mosaic

MY1723ML
See page 85



Taylor

TY1716AN
See page 90



Taylor

TY1721AN
See page 90



Trilogy

TRG1712OZ
See page 95



Trilogy

TRG1716OZ
See page 95



Whitney

WHI1716IS
See page 100



Baron

BRO1715MK
See page 110



Castile

CS1718RK
See page 111



Milbank

MBK1716VG
See page 113



Metropolis

MTP1718AN
See page 117



Tavern

TVN1717DK
See page 120



Palmer

PLR1716PN
See page 122



New Harbor

NHR1718WT
See page 133



Wilder

WLR1716MB
See page 135



Union Station

UST1716WT
See page 140



Semi-Flush Mounts

Please see referenced page numbers for larger images and full descriptions of these products.

PLATINUM COLLECTION

Alexa

PCAX1714C

See page 179



PLATINUM COLLECTION

Crowne

PCCR1717CC

See page 180



PLATINUM COLLECTION

Shimmer

PCSR1716C

See page 181



PLATINUM COLLECTION

Vision

PCVN1716C

See page 182



PLATINUM COLLECTION

Superior

PCSP1718C

See page 184



PLATINUM COLLECTION

Array

PCAY1722C

See page 190



PLATINUM COLLECTION

Abode

PCAE1715C

See page 190



CAROLYN KINDER

Confetti

CKCF17170S/RK

See page 209



CAROLYN KINDER

Confetti

CKCF17200S

See page 209



CAROLYN KINDER

Confetti

CKCF17140S

See page 209



CAROLYN KINDER

Metro

CKMO1716BN

See page 210



CAROLYN KINDER

Marisol

CKMS1716TM

See page 213



UPTOWN COLLECTION
Theater Row

UPTR1716WT
See page 218



UPTOWN COLLECTION
Penn Station

UPPS1713BN/WT
See page 225



Laguna

MC842SRC
See page 228



Kingsford

MCKD1715TM
See page 235



Pearce

PER1715TB
See page 236



Belfair

MCBF1717WT
See page 237



Zen

ZE1717K
See page 239



Arcadia

AI1720IB
See page 240



Aristocrat

AS1716PN
See page 241



Sanibel

SSSB1714VB
See page 245



Please see the **Quoizel Tiffany Collection** on page 459 for many attractive art glass semi-flush mount lighting solutions.

F LUSHMOUNTS

DAMP ML184PN



DAMP ML183A

Melon

FINISH: **A** Antique Brass **ES** Empire Silver
PN Palladian Bronze **W** Fresco

GLASS: Etched Melon



DAMP ML183ES



DAMP ML182PNUL

DAMP ML183W



PRODUCT	DIMENSIONS	BULBS
ML182AUL/ESUL/PNUL/WUL	4.5" H, 10.5" W, 10.5" Dp.	1-75W Med. Base or 18W CFL
ML183A/ES/PN/W	5" H, 13" W, 13" Dp.	2-75W Med. Base or 18W CFL
ML184A/ES/PN/W	6" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL

FLUSH MOUNTS



MNR1611BN DAMP



DAMP MNR1613PN



DAMP MNR1613BN

Manor

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
GLASS: White Alabaster



DAMP MNR1615PN

PRODUCT	DIMENSIONS	BULBS
MNR1611BN/PN	5" H, 11" W, 11" Dp.	1-100W Med. Base or 23W CFL
MNR1613BN/PN	5" H, 13" W, 13" Dp.	2-75W Med. Base or 18W CFL
MNR1615BN/PN	5.5" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL



SMT1612PN DAMP



DAMP **SMT1614PN**



DAMP **SMT1614BN**

Summit

FINISH: **BN** Brushed Nickel
PN Palladian Bronze

GLASS: Opal



DAMP **SMT1617BN**

PRODUCT	DIMENSIONS	BULBS
SMT1612BN/PN	4.5" H, 12" W, 12" Dp.	1-100W Med. Base or 23W CFL
SMT1614BN/PN	5.5" H, 14" W, 14" Dp.	2-75W Med. Base or 18W CFL
SMT1617BN/PN	6" H, 17" W, 17" Dp.	3-75W Med. Base or 18W CFL



GF1617AN DAMP



DAMP **GF1617PN**

Griffin

FINISH: **AN** Antique Nickel
PN Palladian Bronze

GLASS: Etched Painted White Inside

See matching Griffin semi-flush mounts on page 294.



DAMP **GF1621AN**



GF1621PN DAMP

PRODUCT

GF1617AN/PN

DIMENSIONS

7" H, 17" W, 17" Dp.

CANOPY

6" x 1.25"

BULBS

3-100W Med. Base or 23W CFL

GF1621AN/PN

8.5" H, 21" W, 21" Dp.

6" x 1.25"

4-60W Med. Base or 13W CFL



OZ1613IN DAMP



DAMP OZ1613PN

Ozark

FINISH: IN Iron Gate PN Palladian Bronze
GLASS: Etched Painted White Inside

See matching Ozark semi-flush mounts on page 293.



OZ1616IN DAMP



DAMP OZ1616PN

PRODUCT

DIMENSIONS

BULBS

OZ1613IN/PN

5.5" H, 13" W, 13" Dp.

2-60W Med. Base or 13W CFL

OZ1616IN/PN

6.5" H, 16" W, 16" Dp.

3-60W Med. Base or 13W CFL

FLUSH MOUNTS



WLS1613PN DAMP

Wilson

FINISH: Palladian Bronze

GLASS: Clear & Opal Etched



DAMP **WLS1615PN**




Sound

FINISH: Royal Ebony

See matching pendant
BND1818BA on page 268.

BND1613BA DAMP



PRODUCT	DIMENSIONS	CANOPY	BULBS
BND1613BA	7" H, 13.5" W, 13.5" Dp.	.75" x 5.25"	3-40W Vintage Bulb Supplied*
WLS1613PN	7" H, 13" W, 13" Dp.	-	2-75W Med. Base or 18W CFL
WLS1615PN	7.5" H, 15" W, 15" Dp.	-	3-75W Med. Base or 18W CFL

*Max Wattage: 60W Med. Base or 18W CFL

Flush Mounts

Please see referenced page numbers for larger images and full descriptions of these products.

Adonis

ADS1615DC

See page 39



Monterey Mosaic

MY1613ML

See page 85



Monterey Mosaic

MY1618ML

See page 85



Chamber

CHB1612DK

See page 106



Laila

LLA1615RA

See page 116



Opera

OPA1613WT

See page 127



Opera

OPA1617WT

See page 127



PLATINUM COLLECTION

Bordeaux

BRX1614C

See page 175



PLATINUM COLLECTION

Bordeaux

BRX1619C

See page 175



PLATINUM COLLECTION

Bordeaux

BRXA1614C

See page 175



PLATINUM COLLECTION

Bordeaux

BRXA1619C

See page 175



PLATINUM COLLECTION

Bordeaux

BRX1611C

See page 176




PLATINUM COLLECTION

Bordeaux

BRX1620C

See page 176



PLATINUM COLLECTION

Bordeaux

BRX1626C

See page 176



PLATINUM COLLECTION

Countess

PCCT1616C

See page 179



PLATINUM COLLECTION

Countess

PCCT1623C

See page 179



PLATINUM COLLECTION

Paragon

PRN1614C

See page 182



PLATINUM COLLECTION

Highrise

PCHE1616C

See page 183



PLATINUM COLLECTION

Highrise

PCHE1620C

See page 183



PLATINUM COLLECTION

Ella

PCEL1616C

See page 184



PLATINUM COLLECTION

Ella

PCEL1623C

See page 184



PLATINUM COLLECTION

Valla

VLA1618C

See page 185



PLATINUM COLLECTION

Ribbons

RBN1616CRC

See page 187



PLATINUM COLLECTION

Ribbons

RBN1622CRC

See page 187



Flush Mounts

Please see referenced page numbers for larger images and full descriptions of these products.

PLATINUM COLLECTION

Ribbons

RBN1628CRC

See page 187



PLATINUM COLLECTION

Ribbons

RBN1616C/MN/SG/W/WT

See page 189



PLATINUM COLLECTION

Ribbons

RBN1622C/MN/SG/W/WT

See page 189



PLATINUM COLLECTION

Ribbons

RBN1628C/MN/SG/W/WT

See page 189



Laguna

MCLG1612RC

See page 229



Laguna

MCLG1616RC

See page 229



Zen

ZE1617K

See page 239



*Please see the **Quoizel Tiffany Collection** on **page 459** for many attractive art glass flush mount lighting solutions.*



From the **DUCHESS COLLECTION:**
DH1404PN (p.312)

S **RACKLIGHTING**

QUOIZEL

Duchess

FINISH: AN Antique Nickel PN Palladian Bronze
GLASS: AN Grey Marble PN Champagne Marble

Please see pages 52-57
 for matching Duchess
 products.



Also available in PN finish:
DH1404PN DAMP

DAMP **DH1404AN**



All Quoizel Track Lights Swivel

Kyle

FINISH: Imperial Bronze
SHADE: Butterscotch Onyx

Please see pages 68-73
 for matching Kyle products.

QUOIZEL
**NATURALS
 ONYX**

DAMP **KY1404IB**



Monterey Mosaic

FINISH: Malaga
SHADE: Pen Shell Mosaic

Please see pages
 81-86
 for matching
 Monterey Mosaic
 products.

DAMP **MY1404ML**



QUOIZEL
**NATURALS
 PEN SHELL**

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH1404AN/PN	12.5" H, 36.5" W, 6" Dp.	6.5" x 4.5"	4-100W Med. Base or 23W CFL
KY1404IB	14.5" H, 36" W, 4.5" Dp.	8.25" x 4.5"	4-100W Med. Base or 23W CFL
MY1404ML	16.5" H, 43.5" W, 5" Dp.	7.25"	4-100W Med. Base or 23W CFL



PF1405C DAMP

Pacifica

FINISH: Polished Chrome

GLASS: Opal Etched with Wave Pattern

Please see page 359 for matching Pacifica products.



DAMP **QTR10054PN**

Denning

FINISH: Palladian Bronze

SHADE: Metal

All Quoizel Track Lights Swivel



DAMP **EVE1404PN**

Eastvale

FINISH: Palladian Bronze

SHADE: Metal

Please see page 105 for matching Eastvale products.

PRODUCT	DIMENSIONS	CANOPY	BULBS
EVE1404PN	10.5" H, 36.5" W, 3.5" Dp.	7" x 5"	4-50W MR-16 with GU10 Base Shielded Supplied
PF1405C	10.5" H, 44.5" W, 4.5" Dp.	6.5" x 4.5"	5-60W Frosted G9 Halogen Supplied
QTR10054PN	13.5" H, 36" W, 3.5" Dp.	6.5"	4-50W MR-16 with GU10 Base Shielded Supplied



From the **KYLE COLLECTION:**
KY14041B (p. 312)

Asheville

FINISH: Valiant Bronze

Please see pages 470-474 for matching Asheville products.



TFAS1404VA DAMP

DAMP **TFIK1404VA**



Inglenook

FINISH: Valiant Bronze

Please see pages 464-468 for matching Inglenook products.

All Quoizel Track Lights Swivel

Victory

FINISH: Valiant Bronze

Please see pages 460-461 for matching Victory products.

DAMP **TFVY1404VA**



NEW!
FOR ♦ 2016

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFAS1404VA	13.5" H*, 43.5" W, 7" Dp.	5.5" x 1.75"	4-100W Med. Base or 23W CFL	Each Shade Contains 44 Pieces of Tiffany Glass
TFIK1404VA	14" H, 42" W, 6" Dp.	9.5" x 4.5" x .75"	4-100W Med. Base or 23W CFL	Each Shade Contains 184 Pieces of Tiffany Glass
TFVY1404VA	15" H, 43" W, 6" Dp.	6"	4-100W Med. Base or 23W CFL	Each Shade Contains 65 Pieces of Tiffany Glass

*Comes with (2) 6" and (2) 12" Rods.

Taylor

FINISH: **AN** Antique Nickel
WT Western Bronze

GLASS: Opal Etched

Please see pages 87-91
 for matching Taylor products

NEW!
 FOR ♦ 2016



TY1444AN DAMP



NEW!
 FOR ♦ 2016

DAMP **TY1444WT**

All Quoizel Track Lights Swivel

TY1404AN DAMP



PRODUCT	DIMENSIONS	CANOPY	BULBS
TY1404AN	8.5" H, 43" W, 3" Dp.	9" x 4.5" x .875"	4-60W Frosted G9 Halogen Supplied
TY1444AN/WT	11" H, 44" W, 5" Dp.	9" x 4.75"	4-100W Med. Base or 23W CFL

WALL FIXTURES | QUOIZEL



From the **DOWNTOWN COLLECTION: DW8701C**
(p. 49)



LSM8801GY



LSM8801PS

LSM8801TM



Millenium

FINISH: **GY** Gallery Gold
PS Pewter Plated
TM Teco Marrone
SHADE: White Parchment

Yuma

FINISH: Imperial Bronze
GLASS: Amber Scavo




YU8710IB

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS	SHADE DIMS
LSM8801GY	10" H, 10" W, 5.5" Dp.	5.5" x 5.75"	3.5"	1-60W Cand. Base	(4.25" x 7") x (5.25" x 10") x 7"
LSM8801PS/TM	10" H, 9" W, 5.5" Dp.	7" x 7"	3.5"	1-60W Cand. Base	7" x 9" x 5.5"
YU8710IB	8.5" H, 17" W, 9" Dp.	4.5"	2.5"	1-100W Med. Base or 23W CFL	-

Wall Fixtures

Please see referenced page numbers for larger images and full descriptions of these products.




Adonis

ADS8701DC
See page 38



Downtown

DW8701BN/C
See page 49



Duchess

DH8601AN/PN
See page 57



Kendra

KD8701MM
See page 65



Kyle

KY8701IB/IN
See page 73



Kyle

KY8801IN/IB
See page 73




La Parra

LP8601IB
See page 76



Marquette

MQ8701HL
See page 79



Monterey Mosaic

MY8801ML
See page 86



Taylor

TY8501AN
See page 87




Taylor

TY8601C/AN/BN
See page 91




Trilogy

TRG8701OZ
See page 95



Whitney

WHI8701IS
See page 97



Adams

ADA8702LN
See page 103



Armelle

AME8701IB
See page 109



Remi

REM8701C
See page 123

Wall Fixtures

Please see referenced page numbers for larger images and full descriptions of these products.

Noble

NBE8702RK
See page 129



Tricia

TCA8701VP
See page 137



UPTOWN
COLLECTION

East Village

UPEV8701WT
See page 217



UPTOWN COLLECTION

Theater Row

UPTR8701IS/WT
See page 218



UPTOWN COLLECTION

Madison Manor

UPMM8701WT
See page 222



UPTOWN COLLECTION

Seaport

UPSE8701WT
See page 226



UPTOWN
COLLECTION

Holita

UPHL8701IS
See page 226



Inglenook

TFIK8802
See page 468



Stephen

TFST8701VB
See page 480



Classic Craftsman

TFCC8802
See page 506



Bath Lighting

Please see the **Quoizel Bath Lighting Collection** starting on **p. 321** for many additional wall lighting solutions.



From the **TAYLOR COLLECTION:**
TY8501AN (p. 87)



From the
DOWNTOWN COLLECTION:
DW8701C (p.334)
Photo Courtesy of
Regina Sturrock Design, Inc.
www.reginasturrockdesign.com

NEW!
FOR ♦ 2016

Quoizel now offers styles that are compatible with retro-fit LED bulbs, styles with LED bulbs supplied and integrated LED products which are indicated by the logo to the right.

INTEGRATED LED
10 YEAR WARRANTY


Bram COLLECTION

NEW!

FOR ♦ 2016

FINISH: Polished Chrome

GLASS: opal etched



PCBM8520C DAMP

Enlarged for detail

PLATINUM
by QUOIZEL

INTEGRATED LED

10 YEAR WARRANTY



PCBM8505C DAMP



PCBM8526C DAMP

OPTIC
GLASS

LED CHART

	PCBM8505C	PCBM8520C	PCBM8526C
Lumens	880	2138	2996
Total Watts	12W	25.5W	36W
Color Rendering Index (CRI)	90	90	90
Color Temperature (CCT)	2700K	3000K	3000K
Dimmable	Yes	Yes	Yes

Bram COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCBM8505C	13.5" H, 5.5" W, 3.5" Ext.	4.5" x 4.5"	8.75"	See LED chart
PCBM8520C	5.5" H, 20.5" W, 3.5" Ext.	4.5" x 4.5"	3"	See LED chart
PCBM8526C	5.5" H, 26.5" W, 3.5" Ext.	4.5" x 4.5"	3"	See LED chart

Bram bath fixtures can be mounted horizontally or vertically.

Pierre

FINISH: Brushed nickel
GLASS: optic

INTEGRATED LED

10 YEAR WARRANTY

Bath lighting

PCPR8522BN

Enlarged for detail

MOUNTS

MOUNTS



PCPR8530BN



LED CHART

	PCPR8522	PCPR8530
Lumens	1800	2200
Total Watts	20W	28W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes



PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

PCED8517C

Enlarged for detail

INTEGRATED LED

10 YEAR WARRANTY

Endless

FINISH: Polished Chrome
GLASS: optic, Sandblasted inside

MOUNTS

PCED8528C



PCED8521C

LED CHART

	PCED8517	PCED8521	PCED8528
Lumens	1200	1800	2500
Total Watts	12W	18W	25W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3000K	3000K	3000K
Dimmable	Yes	Yes	Yes

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCED8517C	4.5" H, 17.5" W, 4.5" Ext.	17.37" x 4.37"	2.18"	See LED chart
PCED8521C	4.5" H, 21.5" W, 4.5" Ext.	21.25" x 4.37"	2.18"	See LED chart
PCED8528C	4.5" H, 29" W, 4.5" Ext.	28.75" x 4.37"	2.18"	See LED chart
PCPR8522BN	4.5" H, 22" W, 4" Ext.	4.5" x 7"	2.5"	See LED chart
PCPR8530BN	4.5" H, 30" W, 4" Ext.	4.5" x 7"	2.5"	See LED chart

Pierre bath fixtures can be mounted horizontally or vertically.

Valiant


NEW!
FOR ♦ 2016

FINISH: Brushed nickel
GLASS: Clear etched inside

PCVT8518BN

Enlarged for detail

MOUNTS



PCVT8524BN

LED CHART

	PCVT8518BN	PCVT8524BN
Lumens	1565	2020
Total Watts	21W	39W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes

PLATINUM
by QUOIZEL

INTEGRATED LED

10 YEAR WARRANTY

Blade

NEW!
FOR ♦ 2016

FINISH: Polished Chrome
GLASS: opal etched



PCBD8519C

MOUNTS

PCBD8526C

LED CHART

	PCBD8519C	PCBD8526C
Lumens	1830	2565
Total Watts	25W	33W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	2700K	2700K
Dimmable	Yes	Yes

Enlarged for detail



PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCBD8519C	5" H, 19" W, 4.5" Ext.	4.75" x 6.75"	2.5"	See LED chart
PCBD8526C	5" H, 26" W, 4.5" Ext.	4.75" x 6.75"	2.5"	See LED chart
PCVT8518BN	5" H, 18" W, 3.5" Ext.	4.5" x 5.75"	2.5"	See LED chart
PCVT8524BN	5" H, 24" W, 3.5" Ext.	4.5" x 5.75"	2.5"	See LED chart

Valiant and Blade bath fixtures can be mounted horizontally or vertically.



Pace

FINISH: Polished Chrome
GLASS: Opal Etched Inner, Clear Outer

PCPC8527C DAMP

Enlarged for detail



DAMP **PCPC8533C**



LED CHART

	PCPC8527C	PCPC8533C
Lumens	2060	2740
Total Watts	32W	42W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes



Promenade

FINISH: Polished Chrome
GLASS: Acrylic Rectangular

PCPE8524C DAMP

Enlarged for detail

MOUNTS

MOUNTS

LED CHART

	PCPE8524C	PCPE8536C
Lumens	960	1440
Total Watts	8W	12W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes



PCPE8536C DAMP

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCPC8527C	4.5" H, 26.5" W, 4" Ext.	7" x 4.5"	2.5"	See LED chart
PCPC8533C	4.5" H, 33" W, 4" Ext.	7" x 4.5"	2.5"	See LED chart
PCPE8524C	4.5" H, 24" W, 3" Ext.	7" x 4.5"	2.5"	See LED chart
PCPE8536C	4.5" H, 37" W, 3" Ext.	7" x 4.5"	2.5"	See LED chart

Promenade bath fixtures can be mounted horizontally or vertically.

DAMP PCDH8522BN



Dash

FINISH: Brushed Nickel
GLASS: White

DAMP PCDH8530BN

LED CHART

	PCDH8522BN	PCDH8530BN
Lumens	1600	2240
Total Watts	20W	28W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	Yes	Yes



10 YEAR WARRANTY



Glacial

FINISH: Polished Chrome
GLASS: Clear, Sandblasted Inside

DAMP PCGL8522BN

Enlarged for detail



LED CHART

	PCGL8522BN	PCGL8530BN
Lumens	1700	3200
Total Watts	22W	30W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	2700K	2700K
Dimmable	Yes	Yes



DAMP PCGL8530BN

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCDH8522BN	4.5" H, 22" W, 3.5" Ext.	21.5" x 4.5"	2.5"	See LED chart
PCDH8530BN	4.5" H, 30" W, 3.5" Ext.	29.5" x 4.5"	2.5"	See LED chart
PCGL8522BN	5" H, 22" W, 5" Ext.	6" x 5"	2.5"	See LED chart
PCGL8530BN	5.5" H, 30" W, 5" Ext.	6.75" x 5.5"	2.5"	See LED chart

Dash and Glacial bath fixtures can be mounted horizontally or vertically.



CRYSTAL ♦ COLLECTION

- ◆ Dramatic lighting created by faceted crystal pendants
- ◆ free of contaminant colors such as iron for clarity and purity allowing the light to radiate to its greatest potential
- ◆ Bulbs are positioned in the most strategic locations, maximizing the radiance of the light emanating through the crystal
- ◆ highly polished mirrored chrome maximizes the reflectivity of the projected light
- ◆ the highest quality g 4 and g 9 bulbs create a great intensity of light

PCAX8603CLED DAMP

Enlarged for detail

Alexa

FINISH: Polished Chrome
GLASS: Crystal

*See matching
Semi-Flush **PCAX1714C**
on page 179.*

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

PCAX8604CLED DAMP



PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
PCAX8603CLED	5" H, 25" W, 4" Ext.	24.37" x 5.12"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
PCAX8604CLED	5" H, 33" W, 4" Ext.	32.25" x 5.12"	3"	4-4.5W Frosted G9 LED Dimmable Supplied

ShimmerCOLLECTION

FINISH:
Polished Chrome

GLASS:
Crystal studded

DAMP PCSR8603CLED

Enlarged for detail



See matching semi-flush
PCSR1716C on page 181.

PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION

MOUNTS



DAMP PCSR8602CLED

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP PCSR8604CLED



ShimmerCOLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSR8602CLED	8" H, 13.5" W, 5.5" Ext.	4.75" x 4.75"	6"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSR8603CLED	8" H, 23" W, 5.5" Ext.	4.75" x 4.75"	6"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSR8604CLED	8" H, 32" W, 5.5" Ext.	4.75" x 4.75"	6"	4-4.5W Frosted G9 LED Dimmable Supplied

Shimmer bath fixtures can be mounted as uplights or downlights.

Seaview COLLECTION

Bath lighting

NEW!

FOR ♦ 2016

FINISH: **BN** Brushed nickel **C** Polished Chrome

GLASS: **BN** Clear thick etched inside **C** Clear thick



DAMP PCSW8602CLED

Enlarged for detail

MOUNTS

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes



PLATINUM
by QUOIZEL

DAMP PCSW8601BNLED



DAMP PCSW8603BNLED



DAMP PCSW8604CLED

Seaview COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSW8601BNLED / CLED	7" H, 5.5" W, 4.5" Ext.	4.75" x 7"	4"	1-4.5W Frosted G9 LED Dimmable Supplied
PCSW8602BNLED / CLED	5.5" H, 14.5" W, 5" Ext.	7" x 4.75"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSW8603BNLED / CLED	5.5" H, 22" W, 5" Ext.	7" x 4.75"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSW8604BNLED / CLED	5.5" H, 30" W, 5" Ext.	7" x 4.75"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Seaview bath fixtures can be mounted as uplights or downlights.

Serena COLLECTION

NEW!

FOR ♦ 2016

FINISH: Brushed nickel

GLASS: Clear

DAMP PCSA8602BNLED

Enlarged for detail



MOUNTS



DAMP PCSA8603BNLED

PLATINUM
by QUOIZEL

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes



DAMP PCSA8604BNLED

Serena COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCSA8602BNLED	6.5" H, 12.5" W, 5.5" Ext.	6.75" x 4.75"	5.12"	2-4.5W Frosted G9 LED Dimmable Supplied
PCSA8603BNLED	6.5" H, 20" W, 5.5" Ext.	6.75" x 4.75"	5.12"	3-4.5W Frosted G9 LED Dimmable Supplied
PCSA8604BNLED	6.5" H, 28" W, 5.5" Ext.	6.75" x 4.75"	5.12"	4-4.5W Frosted G9 LED Dimmable Supplied

Serena bath fixtures can be mounted as uplights or downlights.

Lacombe

FINISH: Polished Chrome
SHADE: Metal Frame with Clear Glass Beads

NEW!
FOR ♦ 2016

PLATINUM

PCLC8603CLED

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS



PCLC8605CLED

PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION



PCMR8603CLED

Enlarged for detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

PCMR8605CLED

Mirabella

FINISH: Polished Chrome
GLASS: Crystal Accents

NEW!
FOR ♦ 2016



PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCLC8603CLED	5" H, 18" W, 5.5" Ext.	14.5" x 4.75"	2.5"	3-4.5W Frosted G9 LED Dimmable Supplied
PCLC8605CLED	5" H, 26" W, 6.5" Ext.	19.5" x 4.75"	2.5"	5-4.5W Frosted G9 LED Dimmable Supplied
PCMR8603CLED	9.5" H, 12" W, 5.5" Ext.	12" x 6"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
PCMR8605CLED	11" H, 24" W, 6" Ext.	24" x 6"	3"	5-4.5W Frosted G9 LED Dimmable Supplied

Lacombe and Mirabella bath fixtures can be mounted as uplights or downlights.

Divine COLLECTION

FINISH: Polished Chrome

GLASS: Clear Crystal

DAMP PCDV8602CLED



detail

NEW!

FOR ♦ 2016

PLATINUM
by QUOIZEL

CRYSTAL ♦ COLLECTION

MOUNTS



DAMP PCDV8603CLED

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP PCDV8604CLED



Divine COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCDV8602CLED	6" H, 13.5" W, 6" Ext.	7" x 4.75"	5.25"	2-4.5W Frosted G9 LED Dimmable Supplied
PCDV8603CLED	6" H, 23" W, 6" Ext.	7.5" x 4.75"	5.25"	3-4.5W Frosted G9 LED Dimmable Supplied
PCDV8604CLED	6" H, 31.5" W, 6" Ext.	7.5" x 4.75"	5.25"	4-4.5W Frosted G9 LED Dimmable Supplied

Divine bath fixtures can be mounted as uplights or downlights.

Devlin COLLECTION


Bath lighting

FINISH: **BN** Brushed nickel **C** Polished Chrome

GLASS: opal

DAMP DVN8602BNLED

Enlarged for detail



LED CHART


Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

DAMP DVN8603CLED



DAMP DVN8604BNLED



Devlin COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DVN8602BNLED/CLED NEW!	6" H, 14" W, 8" Ext.	6.5" x 4.5"	3"	2-4.5W Frosted G9 LED Dimmable Supplied
DVN8603BNLED/CLED NEW!	6" H, 22.5" W, 8" Ext.	6.5" x 4.5"	3"	3-4.5W Frosted G9 LED Dimmable Supplied
DVN8604BNLED/CLED NEW!	6" H, 31.5" W, 8" Ext.	6.5" x 4.5"	3"	4-4.5W Frosted G9 LED Dimmable Supplied

Devlin bath fixtures can be mounted as uplights or downlights.

Downtown COLLECTION

FINISH:

BN Brushed nickel **NEW!** **C** Polished Chrome

GLASS:

opal etched

DAMP DW8603CLED



DAMP DW8602CLED



DAMP DW8701C

Enlarged for detail

MOUNTS

*See matching
Downtown
mirror on
page 532*



DAMP DW8604CLED





DW8701BN DAMP

NEW!
FOR ♦ 2016

DAMP DW8602BNLED



detail

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

(8701 is Non-LED)

MOUNTS



DW8603BNLED DAMP

DAMP DW8604BNLED



Downtown COLLECTION

PRODUCT		DIMENSIONS	CANOPY	HCWO	BULBS
DW8602BNLED/CLED	NEW!	7.5" H, 15" W, 7" Ext.	8" x 5"	5"	2-4.5W Frosted G9 LED Dimmable Supplied
DW8603BNLED/CLED	NEW!	7.5" H, 24.5" W, 7" Ext.	8" x 5"	5"	3-4.5W Frosted G9 LED Dimmable Supplied
DW8604BNLED/CLED	NEW!	7.5" H, 33.5" W, 7" Ext.	8" x 5"	5"	4-4.5W Frosted G9 LED Dimmable Supplied
DW8701BN/C	NEW!	10.5" H, 6" W, 8" Ext.	6" x 6"	7.75"	1-100W Med. Base or 23W CFL

Downtown bath fixtures can be mounted as uplights or downlights.

Erin COLLECTION

FINISH: imperial Bronze

GLASS: opal etched

DAMP ERN8603IBLED

Enlarged for detail



MOUNTS



ERN8602IBLED **DAMP**

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP ERN8604IBLED



Erin COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
ERN8602IBLED NEW!	6" H, 17" W, 5" Ext.	8" x 5"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
ERN8603IBLED NEW!	6" H, 24" W, 5" Ext.	8" x 5"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
ERN8604IBLED NEW!	6" H, 33" W, 5" Ext.	8" x 5"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Erin bath fixtures can be mounted as uplights or downlights.

Tatum COLLECTION

Bath Lighting

FINISH: Brushed nickel

GLASS: opal etched

TU8603BNLED

Enlarged for detail



TU8602BNLED

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

MOUNTS

TU8604BNLED



Tatum COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS
TU8602BNLED NEW!	5" H, 13" W, 5.5" Ext.	7" x 4.5"	2.63"	2-4.5W Frosted G9 LED Dimmable Supplied
TU8603BNLED NEW!	5" H, 21" W, 5.5" Ext.	10" x 4.5"	2.63"	3-4.5W Frosted G9 LED Dimmable Supplied
TU8604BNLED NEW!	5" H, 29" W, 5.5" Ext.	18" x 4.5"	2.63"	4-4.5W Frosted G9 LED Dimmable Supplied

Tatum bath fixtures can be mounted as uplights or downlights.

Quinton COLLECTION

FINISH: Polished Chrome

GLASS: opal etched

QI8603CLED

Enlarged for detail



MOUNTS

QI8602CLED

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

QI8604CLED



Quinton COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
QI8602CLED NEW!	9" H, 14" W, 5" Ext.	7" x 5"	6"	2-4.5W Frosted G9 LED Dimmable Supplied
QI8603CLED NEW!	9" H, 23.5" W, 5" Ext.	7" x 5"	6"	3-4.5W Frosted G9 LED Dimmable Supplied
QI8604CLED NEW!	9" H, 33.5" W, 5" Ext.	7" x 5"	6"	4-4.5W Frosted G9 LED Dimmable Supplied

Quinton bath fixtures can be mounted as uplights or downlights.

Nolan COLLECTION


Bath Lighting

FINISH: Brushed nickel

GLASS: opal etched

DAMP NN8602BNLED

Enlarged for detail



MOUNTS

LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP NN8603BNLED



DAMP NN8604BNLED



Nolan COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
NN8602BNLED NEW!	5.5" H, 19" W, 6" Ext.	7" x 4.5"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
NN8603BNLED NEW!	5.5" H, 26.5" W, 6" Ext.	7" x 4.5"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
NN8604BNLED NEW!	5.5" H, 35.5" W, 6" Ext.	7" x 4.5"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Nolan bath fixtures can be mounted as uplights or downlights.

Kolt COLLECTION

FINISH: Polished Chrome

GLASS:

outer: Clear inner: heavy sandblasted

DAMP KLT8603CLED

Enlarged for detail



MOUNTS



LED CHART

Lumens	400
Total Watts	4.5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	Yes

DAMP KLT8602CLED

DAMP KLT8604CLED



Kolt COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
KLT8602CLED NEW!	6" H, 13" W, 6.5" Ext.	6.5" x 6"	3.5"	2-4.5W Frosted G9 LED Dimmable Supplied
KLT8603CLED NEW!	6" H, 21" W, 6.5" Ext.	6.5" x 6"	3.5"	3-4.5W Frosted G9 LED Dimmable Supplied
KLT8604CLED NEW!	6" H, 29" W, 6.5" Ext.	6.5" x 6"	3.5"	4-4.5W Frosted G9 LED Dimmable Supplied

Kolt bath fixtures can be mounted as uplights or downlights.



From the **KOLT COLLECTION:**
KLT8603CLED

Also shown:
GREYSTONE MIRROR: QR1815
(See p.530)

Adano COLLECTION

FINISH: empire silver

GLASS: opal etched Cased

DAMP AN8539ES

Enlarged for detail



MOUNTS

AN8540ES DAMP



DAMP AN8541ES



Adano COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
AN8539ES	7.5" H, 14" W, 7" Dp.	8" x 4.5"	3"	2-100W Med. Base or 23W CFL
AN8540ES	7.5" H, 21" W, 7" Dp.	8" x 4.5"	3"	3-100W Med. Base or 23W CFL
AN8541ES	7.5" H, 28" W, 7" Dp.	8" x 4.5"	3"	4-100W Med. Base or 23W CFL

Adano bath fixtures can be mounted as uplights or downlights.

Broadgate COLLECTION

Bath lighting

FINISH: Brushed nickel

GLASS: Clear opal

DAMP BGT8602BN

Enlarged for detail



MOUNTS

DAMP BGT8603BN



DAMP BGT8604BN



Broadgate COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
BGT8602BN	10" H, 17.5" W, 9" Dp.	5.25" x 5.25"	5.5"	2-100W Med. Base or 23W CFL
BGT8603BN	10" H, 27" W, 9" Dp.	5.25" x 5.25"	5.5"	3-100W Med. Base or 23W CFL
BGT8604BN	10" H, 36" W, 9" Dp.	5.25" x 5.25"	5.5"	4-100W Med. Base or 23W CFL

Broadgate bath fixtures can be mounted as uplights or downlights.



From the **DUBLIN COLLECTION**
Bath Fixture: **DBN8603BN**

Dublin COLLECTION

Bath lighting

FINISH:
Brushed nickel
GLASS:
Clear Pressed

See matching mini-pendant
DBN1506BN on page 282.



detail

DBN8602BN DAMP

MOUNTS

NEW!
FOR ♦ 2016



DBN8603BN DAMP

DAMP **DBN8604BN**



Dublin COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS
DBN8602BN	9" H, 16" W, 8" Ext.	8" x 4.5"	4.5"	2-100W Med. Base or 23W CFL
DBN8603BN	9" H, 25" W, 8" Ext.	8" x 4.5"	4.5"	3-100W Med. Base or 23W CFL
DBN8604BN	9" H, 34.5" W, 8" Ext.	8" x 4.5"	4.5"	4-100W Med. Base or 23W CFL

Bower bath fixtures can be mounted as uplights or downlights.

Bower COLLECTION

FINISH:

Brushed nickel

GLASS:

Opal etched


DAMP BWR8603BN

Enlarged for detail



MOUNTS

DAMP BWR8602BN



BWR8604BN **DAMP**



Bower COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
BWR8602BN	9.5" H, 13" W, 7" Dp.	5" x 5"	7"	2-100W Med. Base or 23W CFL
BWR8603BN	9.5" H, 21.5" W, 7" Dp.	5" x 5"	7"	3-100W Med. Base or 23W CFL
BWR8604BN	9.5" H, 28.5" W, 7" Dp.	5" x 5"	7"	4-100W Med. Base or 23W CFL

Bower bath fixtures can be mounted as uplights or downlights.

Duchess COLLECTION

Bath lighting

FINISH:

AN antique nickel **PN** Palladian Bronze

GLASS:

AN grey Marble **PN** Champagne Marble



DH8601PN DAMP

See matching Duchess styles on page 52-57



See matching Duchess mirrors on page 530

DAMP **DH8603AN**

Enlarged for detail



MOUNTS



DH8602PN DAMP

DAMP **DH8604AN**



Duchess COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DH8601AN/PN	11" H, 6" W, 8" Ext.	4.75" x 6.75"	7.5"	1-100W Med. Base or 23W CFL
DH8602AN/PN	11" H, 16" W, 7.5" Ext.	9" x 5"	7.5"	2-100W Med. Base or 23W CFL
DH8603AN/PN	11" H, 23" W, 7.5" Ext.	9" x 5"	7.5"	3-100W Med. Base or 23W CFL
DH8604AN/PN	11" H, 31.5" W, 7.5" Ext.	9" x 5"	7.5"	4-100W Med. Base or 23W CFL

Duchess bath fixtures can be mounted as uplights or downlights. Duchess mirrors can be hung vertically or horizontally.

Hollister COLLECTION

FINISH: Polished Chrome

GLASS: opal etched

DAMP

HS8603C

Enlarged for detail



MOUNTS



HS8602C DAMP

HS8604C DAMP



DAMP

HS8601C

Hollister COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
HS8601C	9.5" H, 5" W, 7.5" Ext.	5" x 7"	5.5"	1-100W Med. Base or 23W CFL
HS8602C	9.5" H, 14.5" W, 7.5" Ext.	6.75" x 4.75"	7"	2-100W Med. Base or 23W CFL
HS8603C	9.5" H, 23" W, 7.5" Ext.	6.75" x 4.75"	7"	3-100W Med. Base or 23W CFL
HS8604C	9.5" H, 32.5" W, 7.5" Ext.	6.75" x 4.75"	7"	4-100W Med. Base or 23W CFL

Hollister bath fixtures can be mounted as uplights or downlights.

Deluxe COLLECTION

Bath lighting

FINISH: Polished Chrome

GLASS: White Linen



DX8602C



DX8601C

See matching island light **DX348C** on p. 261 and semi-flush **DX1718C** on p. 290.

MOUNTS



DX8603C

Enlarged for detail



DX8604C

Deluxe COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DX8601C	9" H, 6" W, 7.5" Ext.	4.5" x 6.5"	7"	1-100W Med. Base or 23W CFL
DX8602C	10" H, 18" W, 7.5" Ext.	6.25" x 4.5"	8"	2-100W Med. Base or 23W CFL
DX8603C	10" H, 25.5" W, 7.5" Ext.	6.25" x 4.5"	8"	3-100W Med. Base or 23W CFL
DX8604C	10" H, 33.5" W, 7.5" Ext.	6.25" x 4.5"	8"	4-100W Med. Base or 23W CFL

Deluxe bath fixtures can be mounted as uplights or downlights.

Edison COLLECTION

FINISH: Western Bronze

GLASS: seedy

EDS8601WT

Enlarged for detail



VINTAGE STYLE
bulb included



EDS8602WT

MOUNTS

EDS8603WT



EDS8604WT

Edison COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
EDS8601WT	10" H, 5" W, 6.5" Ext.	5" x 5"	8.5"	1-60W Vintage Bulb Supplied*
EDS8602WT	10" H, 16" W, 5.5" Ext.	7.5" x 4.5"	8.5"	2-60W Vintage Bulb Supplied*
EDS8603WT	10" H, 23" W, 7" Ext.	7.5" x 4.5"	8.5"	3-60W Vintage Bulb Supplied*
EDS8604WT	10" H, 32.5" W, 7" Ext.	7.5" x 4.5"	8.5"	4-60W Vintage Bulb Supplied*

Edison bath fixtures can be mounted as uplights or downlights. *Max Wattage: 100W Med. Base or 23W CFL.

Garrison COLLECTION

Bath lighting

FINISH:

BN Brushed nickel **WT** Western Bronze

GLASS:

opal etched

NEW!
FOR ♦ 2016



GRN8603BN

MOUNTS

See matching Garrison mini-pendants **QPP2049BN/WT** on page 279.



GRN8602WT



GRN8604WT

Garrison COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
GRN8602BN/WT	7" H, 16.5" W, 9" Ext.	9" x 4.5"	4"	2-100W Med. Base or 23W CFL
GRN8603BN/WT	7" H, 25" W, 9" Ext.	9" x 4.5"	4"	3-100W Med. Base or 23W CFL
GRN8604BN/WT	7" H, 33.5" W, 9" Ext.	9" x 4.5"	4"	4-100W Med. Base or 23W CFL

Garrison bath fixtures can be mounted as uplights or downlights.

Demitri COLLECTION

FINISH: Polished Chrome

GLASS: White seedy sandstone



MOUNTS

DI8502C DAMP

Enlarged for detail



DI8503C DAMP

DAMP **DI8504C**



Demitri COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DI8502C	8" H, 18" W, 8" Ext.	8" x 4.5"	5.5"	2-100W Med. Base or 23W CFL
DI8503C	8.5" H, 26" W, 8" Ext.	8" x 4.5"	5.5"	3-100W Med. Base or 23W CFL
DI8504C	8.5" H, 35.5" W, 8" Ext.	8" x 4.5"	5.5"	4-100W Med. Base or 23W CFL

Demitri bath fixtures can be mounted as uplights or downlights.



From the
DEMITRI COLLECTION
Bath Fixture: **DI8503ES**

Demitri COLLECTION

FINISH: empire silver

GLASS: o pal etched

DI8503ES DAMP

Enlarged for detail



MOUNTS

DI8502ES DAMP

DI8504ES DAMP



Demitri COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
DI8502ES	8" H, 18" W, 8" Ext.	8" x 4.5"	5.5"	2-100W Med. Base or 23W CFL
DI8503ES	8.5" H, 26" W, 8" Ext.	8" x 4.5"	5.5"	3-100W Med. Base or 23W CFL
DI8504ES	8.5" H, 35.5" W, 8" Ext.	8" x 4.5"	5.5"	4-100W Med. Base or 23W CFL

Demitri bath fixtures can be mounted as uplights or downlights.

FINISH: Polished Chrome

GLASS: Clear sandblasted inside

DAMP LFT8603C

Enlarged for detail



MOUNTS

DAMP LFT8602C



DAMP LFT8604C



PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
LFT8602C	7.5" H, 15" W, 6.5" Ext.	6" x 4.5"	5.5"	2-100W Med. Base or 23W CFL
LFT8603C	7.5" H, 24" W, 6.5" Ext.	6" x 4.5"	5.5"	3-100W Med. Base or 23W CFL
LFT8604C	7.5" H, 34" W, 6.5" Dp.	6" x 4.5"	5.5"	4-100W Med. Base or 23W CFL

Loft bath fixtures can be mounted as uplights or downlights.

Melody COLLECTION

FINISH: Brushed Nickel

GLASS: Mottled textured

DAMP MLD8603BN

Enlarged for detail



detail



DAMP MLD8602BN

MOUNTS

DAMP MLD8604BN



Melody COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
MLD8602BN	6.5" H, 15" W, 5.5" Ext.	9" x 5.75"	3.5"	2-100W Med. Base or 23W CFL
MLD8603BN	6.5" H, 24" W, 5.5" Ext.	9" x 5.75"	3.5"	3-100W Med. Base or 23W CFL
MLD8604BN	6.5" H, 33" W, 5.5" Ext.	9" x 5.75"	3.5"	4-100W Med. Base or 23W CFL

Melody bath fixtures can be mounted as uplights or downlights.

Menlo COLLECTION

Bath Lighting

FINISH:
imperial silver

See matching chandelier
MNO5006WT on page 167.



NEW!
FOR ♦ 2016

MNO8602IS DAMP

Enlarged for detail



detail



MNO8603IS DAMP

MOUNTS

DAMP **MNO8604IS**



Menlo COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS
MNO8602IS	9" H, 12.5" W, 4.5" Ext.	5.25" x 5.25"	7"	2-60W Vintage Bulbs Supplied*
MNO8603IS	9" H, 21" W, 4.5" Ext.	5.25" x 5.25"	6"	3-60W Vintage Bulbs Supplied*
MNO8604IS	9" H, 30.5" W, 4.5" Ext.	5.25" x 5.25"	6"	4-60W Vintage Bulbs Supplied*

Menlo bath fixtures can be mounted as uplights or downlights. *Max Wattage: 100W Med. Base or 23W CFL



From the **PACIFICA COLLECTION:**
PF8603ES

Pacifica COLLECTION

Bath lighting

FINISH: empire silver

GLASS: opal etched with Wave Pattern

MOUNTS



PF8602ES DAMP

Enlarged for detail

See matching track light
PF1405C on page 313.

DAMP **PF8603ES**



DAMP **PF8604ES**



Pacifica COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PF8602ES	6.5" H, 16" W, 6.5" Ext.	6.5" x 4.5"	4.5"	2-100W Med. Base or 23W CFL
PF8603ES	6.5" H, 25" W, 6.5" Ext.	6.5" x 4.5"	4.5"	3-100W Med. Base or 23W CFL
PF8604ES	6.5" H, 33.5" W, 6.5" Ext.	6.5" x 4.5"	4.5"	4-100W Med. Base or 23W CFL

Pacifica bath fixtures can be mounted as uplights or downlights.

Nicholas COLLECTION

FINISH:


BN Brushed nickel **C** Polished Chrome **HO** Harbor Bronze

GLASS:

Opal etched



DAMP NL8602C



DAMP NL8601HO

Enlarged for detail

DAMP NL8604C



DAMP NL8603BN

Enlarged for detail

MOUNTS



Nicholas COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
NL8601BN/C/HO	10" H, 5" W, 7" Ext.	4.5" x 8"	5"	1-100W Med. Base or 23W CFL
NL8602BN/C/HO	10" H, 15" W, 7" Ext.	8" x 4.5"	3.5"	2-100W Med. Base or 23W CFL
NL8603BN/C/HO	10" H, 22" W, 7" Ext.	8" x 4.5"	3.5"	3-100W Med. Base or 23W CFL
NL8604BN/C/HO	10" H, 30.5" W, 7" Ext.	8" x 4.5"	3.5"	4-100W Med. Base or 23W CFL

Nicholas bath fixtures can be mounted as uplights or downlights.

North Gate COLLECTION

Bath lighting


FINISH:
Brushed nickel
GLASS:
opal etched

DAMP NGT8603BN



DAMP NGT8602BN

Enlarged for detail



MOUNTS

DAMP NGT8604BN



North Gate COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
NGT8602BN	7" H, 12" W, 6" Ext.	8" x 5"	4"	2-100W Med. Base or 23W CFL
NGT8603BN	7" H, 20" W, 6" Ext.	8" x 5"	4"	3-100W Med. Base or 23W CFL
NGT8604BN	7" H, 27.5" W, 6" Ext.	8" x 5"	4"	4-100W Med. Base or 23W CFL

North Gate bath fixtures can be mounted as uplights or downlights.

Parallel COLLECTION

FINISH: Polished nickel

GLASS: opal etched



PRL8603PK

MOUNTS

PRL8601PK



PRL8602PK



Parallel COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PRL8601PK	8.5" H, 8.5" W, 5.5" Ext.	6" x 4.5"	5.75"	1-100W Med. Base or 23W CFL
PRL8602PK	8.5" H, 19" W, 5.5" Ext.	8" x 4.5"	5.75"	2-100W Med. Base or 23W CFL
PRL8603PK	8.5" H, 30" W, 5.5" Ext.	8" x 4.5"	5.75"	3-100W Med. Base or 23W CFL

Parallel bath fixtures can be mounted as uplights or downlights.

Supreme COLLECTION

Bath lighting

FINISH:

Polished Chrome

GLASS:

etched with Painted White inside

NEW!

FOR ♦ 2016



SPR8601C DAMP



SPR8602C DAMP

MOUNTS



SPR8604C DAMP



SPR8603C DAMP

Enlarged for detail

CRYSTAL FINIALS

Supreme COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
SPR8601C	8" H, 5" W, 5.5" Ext.	4.75" x 8"	4.25	1-100W Med. Base or 23W CFL
SPR8602C	8" H, 14.5" W, 5.5" Ext.	4.75" x 8"	5.5	2-100W Med. Base or 23W CFL
SPR8603C	8" H, 22" W, 5.5" Ext.	4.75" x 8"	5.5	3-100W Med. Base or 23W CFL
SPR8604C	8" H, 31" W, 5.5" Ext.	4.75" x 8"	5.5	4-100W Med. Base or 23W CFL

Supreme bath fixtures can be mounted as uplights or downlights.

Tritan COLLECTION

FINISH:

Brushed nickel

GLASS:

Opal etched



TT8743BN

Enlarged for detail



TT8742BN



MOUNTS



TT8604BN



Tritan COLLECTION

PRODUCT.	DIMENSIONS	BACKPLATE	HCWO	BULBS
TT8604BN	10" H, 30.5" W, 7.5" Ext.	9" x 4.5"	6"	4-100W Med. Base or 23W CFL
TT8742BN	9" H, 13" W, 7.5" Ext.	9" x 4.5"	6"	2-100W Med. Base or 23W CFL
TT8743BN	9" H, 22" W, 7.5" Ext.	9" x 4.5"	6"	3-100W Med. Base or 23W CFL

Tritan bath fixtures can be mounted as uplights or downlights.

Tranquil Bay COLLECTION

Bath Lighting

FINISH:
Polished Chrome

GLASS:
opal etched

TB8601C

Enlarged for detail

MOUNTS



TB8602C

TB8603C



TB8604C



Tranquil Bay COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
TB8601C	6.5" H, 9" W, 7" Ext.	5" x 5"	4"	1-100W Med. Base or 23W CFL
TB8602C	6.5" H, 18" W, 7" Ext.	5" x 5"	4"	2-100W Med. Base or 23W CFL
TB8603C	6.5" H, 26" W, 7" Ext.	5" x 5"	4"	3-100W Med. Base or 23W CFL
TB8604C	6.5" H, 34" W, 7" Ext.	5" x 5"	4"	4-100W Med. Base or 23W CFL

Tranquil Bay bath fixtures can be mounted as uplights or downlights.



From the **TAYLOR COLLECTION**
Bath Fixture: **TY8603AN** Mirror: **TY43625AN**

Taylor COLLECTION

Bath lighting

FINISH:

AN antique nickel **BN** Brushed nickel **NEW!**

C Polished Chrome **WT** Western Bronze

GLASS: opal etched

DAMP TY8601AN



DAMP TY8603BN

Enlarged for detail



NEW!

FOR ♦ 2016

MOUNTS



See matching Taylor mirror on page 530

DAMP TY8602BN



DAMP TY8604WT



detail

Taylor COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
TY8601AN/BN/C	7.5" H, 4.5" W, 5.5" Dp.	4.5" x 5"	5"	1-100W Med. Base or 23W CFL
TY8602AN/BN/C/WT	7.5" H, 13.5" W, 4.5" Dp.	7" x 4.5"	5.5"	2-100W Med. Base or 23W CFL
TY8603AN/BN/C/WT	7.5" H, 21" W, 5.5" Dp.	7" x 4.5"	5.5"	3-100W Med. Base or 23W CFL
TY8604AN/BN/C/WT	7.5" H, 30" W, 5.5" Dp.	7" x 4.5"	5.5"	4-100W Med. Base or 23W CFL



Taylor bath fixtures can be mounted as uplights or downlights.

Paragon COLLECTION

FINISH:

Polished Chrome

See matching flush mount **PRN1614C** on page 182.



DAMP PRN8606C

Enlarged for detail



DAMP PRN8604C

DAMP PRN8608C



Paragon COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PRN8604C	4.5" H, 14.5" W, 4" Ext.	7" x 5"	2.5"	4-20W Clear G4 Xenon Supplied
PRN8606C	5" H, 21.5" W, 4" Ext.	7" x 5"	2.5"	6-20W Clear G4 Xenon Supplied
PRN8608C	5" H, 28.5" W, 4" Ext.	7" x 5"	2.5"	8-20W Clear G4 Xenon Supplied

Evermore COLLECTION

Bath Lighting

FINISH: Polished Chrome

SHADE: Crystal

EME8604C

Enlarged for detail



PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

FACETED
CRYSTALS



EME8606C



EME8608C

Evermore COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
EME8604C	5" H, 16" W, 6" Ext.	7" x 4.5"	2.5"	4-20W Clear G4 Xenon Supplied
EME8606C	5" H, 23.5" W, 6" Ext.	7" x 4.5"	2.5"	6-20W Clear G4 Xenon Supplied
EME8608C	5" H, 31" W, 6" Ext.	7" x 4.5"	2.5"	8-20W Clear G4 Xenon Supplied



Royale COLLECTION

FINISH: Polished Chrome

SHADE: Crystal



DAMP RYE8604C *Enlarged for detail*



detail

DAMP RYE8605C



Royale COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
RYE8604C	5" H, 20" W, 5" Ext.	7" x 4.5"	2.5"	4-20W Clear G4 Xenon Supplied
RYE8605C	5" H, 24" W, 5" Ext.	7" x 4.5"	2.5"	5-20W Clear G4 Xenon Supplied

From the **BOOKER COLLECTION:**
BKR8408K (p. 404-405)

QUOIZEL



OUTDOOR **LIGHTING**


Monument COLLECTION

FINISH:
Western Bronze

NEW!
FOR ♦ 2016



MNT8404WT 



INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	475
Total Watts	5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



 **MNT8405WT**

Monument COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
MNT8404WT	14" H, 5" W, 4" Dp.	5.25" x 5.25"	7"	See LED chart
MNT8405WT	17.5" H, 6" W, 4" Dp.	5.25" x 5.25"	8.5"	See LED chart

Newbury COLLECTION

o u t d o o r

FINISH:
Mystic Black

GLASS:
Clear Seedy

NEW!

FOR ♦ 2016

WET NYL8407K



NYL1911K **DAMP**

**INDOOR
OUTDOOR**



NYL8409K **WET**



LED CHART

NYL8407K / NYL8409K

Lumens	880
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

INTEGRATED LED

10 YEAR WARRANTY

S·O·L·I·D
BRASS

LED CHART

NYL1911K / NYL8411K / NYL9011K

Lumens	1280
Total Watts	16W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

NYL8411K **WET**

Enlarged for detail



WET NYL9011K



Newbury COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	Light Source
NYL1911K	19" H, 10.5" W, 10.5" Dp.	5"	-	See LED chart
NYL8407K	12" H, 7" W, 7" Ext	4.75" x 5.5"	6"	See LED chart
NYL8409K	13.5" H, 8" W, 8" Ext	4.75" x 5.5"	7"	See LED chart
NYL8411K	20" H, 10.5" W, 10" Ext	4.5" x 9.25"	10"	See LED chart
NYL9011K	21" H, 11" W, 11" Dp.	-	-	See LED chart

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Newbury COLLECTION

FINISH:

K Mystic Black **P** Pewter **Z** Medici Bronze

GLASS:

Clear Seedy

WET NY8416Z

Our Newbury Collection is available in attractive SEEDY glass in 3 finishes!



TITLE 24 **WET** NY8407P



S·O·L·I·D
BRASS

NY8411P **WET**



NY8409K **WET** **TITLE 24**



NY1615K **DAMP**

WET NY8412Z





NY1909Z **DAMP**



NY1912P **DAMP**



NY1916K **DAMP**

INDOOR
OUTDOOR

S·O·L·I·D
BRASS



NY9011K **WET**



WET NY9012P



WET NY9016Z

Newbury COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	FINISHES
NY1615	8" H, 15.5" W, 15.5" Dp.	14"	-	3-40W Cand. Base	K, P, Z
NY1909	19" H, 10.5" W, 10.5" Dp	5"	-	2-60W Cand. Base	K, P, Z
NY1912	21" H, 12.5" W, 12.5" Dp.	5"	-	3-60W Cand. Base	K, P, Z
NY1916	26.5" H, 16" W, 16" Dp.	5"	-	4-60W Cand. Base	K, P, Z
NY8407	12" H, 7" W, 7" Dp.	4.75" x 5.5"	6"	1-150W Med. Base or 40W CFL	K, P, Z
NY8409	13.5" H, 8" W, 8" Ext.	4.75" x 5.5"	7"	1-150W Med. Base or 40W CFL	K, P, Z
NY8411	20" H, 10.5" W, 10" Ext.	4.5" x 9.25"	10"	2-60W Cand. Base	K, P, Z
NY8412	22.5" H, 12.5" W, 11.5" Ext.	4.5" x 9.25"	10"	3-60W Cand. Base	K, P, Z
NY8416	29" H, 16" W, 15" Ext.	5.25" x 12.5"	12"	4-60W Cand. Base	K, P, Z
NY9011	21" H, 11" W x 11" Dp.	-	-	2-60W Cand. Base	K, P, Z
NY9012	23" H, 12" W, 12" Dp.	-	-	3-60W Cand. Base	K, P, Z
NY9016	29.5" H, 16" W, 16" Dp.	-	-	4-60W Cand. Base	K, P, Z

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Finishes Guide:

K=Mystic Black P=Pewter Z=Medici Bronze

24 To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Newbury COLLECTION

One of our most popular and expansive outdoor lines, the **Newbury Collection**, is available in 12 styles, each style in a number of attractive finishes. As we can only show a partial representation on these pages, please refer to the chart on the next page as a complete resource for dimensions and bulb/wattage information.

WET NY8339P



S·O·L·I·D
BRASS



NY8317B

Finish: Polished Brass
Glass: Clear Beveled



NY8315B

S·O·L·I·D
BRASS



NY1794Z

Finish: Medici Bronze
Glass: Clear Beveled



NY9042Z

The Newbury products on these pages represent a sampling of the 12 different styles offered in 6 different finishes.

Please refer to the chart below for dimensions and bulb/wattage information.

Newbury COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	FINISHES
NY1178	19" H, 11" W, 11" Dp.	5"	-	2-60W Cand. Base	A, AC, B, K, P, Z
NY1179	21" H, 12.5" W, 12.5" Dp.	5"	-	3-60W Cand. Base	A, AC, B, K, P, Z
NY1180	26.5" H, 16" W, 16" Dp.	5"	-	4-60W Cand. Base	A, AC, B, K, P, Z
NY1794	8" H, 15.5" W, 15.5" Dp.	-	-	3-40W Cand. Base	B, K, P, Z
NY8315	12.5" H, 7" W, 7" Ext.	4.75" x 5.5"	6"	1-150W Med. Base or 40W CFL	A, AC, B, K, P, Z
NY8316	14" H, 9" W, 8" Ext.	4.75" x 5.5"	7"	1-150W Med. Base or 40W CFL	A, AC, B, K, P, Z
NY8317	20" H, 11" W, 10" Ext.	4.5" x 9.25"	10"	2-60W Cand. Base	A, AC, B, K, P, Z
NY8318	22.5" H, 12.5" W, 11.5" Ext.	4.5" x 9.25"	10"	3-60W Cand. Base	A, AC, B, K, P, Z
NY8339	29" H, 16" W, 15" Ext.	5.25" x 12.5"	12"	4-60W Cand. Base	A, AC, B, K, P, Z
NY9042	21" H, 11" W x 11" Dp.	-	-	2-60W Cand. Base	A, AC, B, K, P, Z
NY9043	23" H, 12.5" W, 12.5" Dp.	-	-	3-60W Cand. Base	A, AC, B, K, P, Z
NY9045	30.5" H, 16" W, 16" Dp.	-	-	4-60W Cand. Base	A, AC, B, K, P, Z

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Finishes Guide:

A=Antique Brass **AC**=Aged Copper **B**=Polished Brass
K=Mystic Black **P**=Pewter **Z**=Medici Bronze

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Newbury COLLECTION



WET NY9045K

WET NY8318K

S·O·L·I·D
BRASS

Finish: Mystic Black
Glass: Clear Beveled



The Newbury products on these pages represent a sampling of the 12 different styles offered in 6 different finishes.

Please refer to the chart on page 377 for dimensions and bulb/wattage information.

DAMP NY1178A



Finish: Antique Brass
Glass: Clear Beveled

NY9043A **WET**



S·O·L·I·D
BRASS



NY8317P WET

Finish: Pewter
Glass: Clear Beveled



TITLE 24 **NY8316P** WET

S·O·L·I·D
BRASS

The Newbury products on these pages represent a sampling of the 12 different styles offered in 6 different finishes. Please refer to the chart on page 377 for dimensions and bulb/wattage information.



NY1180AC DAMP

Finish: Aged Copper
Glass: Clear Beveled

S·O·L·I·D
COPPER



NY1179AC DAMP

OUTDOOR



ALT8407WT **WET**



ALT8405WT **WET**

Alto

FINISH: Western Bronze
GLASS: Clear Seedy

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

	ALT8405WT	ALT8407WT	RYD8408WT
Lumens	825	1645	1028
Total Watts	10W	21W	15W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3000K	3000K	3000K
Dimmable	Yes	Yes	Yes

Ryland

FINISH: Western Bronze
GLASS: Opal etched

WET RYD8408WT



PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
ALT8405WT	15" H, 5.5" W, 5.5" Ext.	4.5" x 6.5"	7.5"	See LED Chart
ALT8407WT	20" H, 7" W, 7" Ext.	5" x 8.5"	8"	See LED Chart
RYD8408WT	13" H, 8" W, 4" Ex.	4.75" x 4.75"	11"	See LED Chart

Cole

FINISH: Western Bronze

ETCHED
GLASS



COE8305WT WET

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

COE8305WT / COE8405WT

Lumens	1985
Total Watts	12W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	Yes



WET **COE8405WT**

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
COE8305WT	10" H, 5" W, 5" Ext.	4.5" x 4.5"	5"	See LED Chart
COE8405WT	13" H, 5" W, 5.5" Ext.	4.5" x 5"	6.5"	See LED Chart

Stonington COLLECTION

FINISH:

K Mystic Black **PN** Palladian Bronze

GLASS:

Clear Water

NEW!

FOR ♦ 2016



5 YEAR WARRANTY



WET SNNL8409K

INTEGRATED LED
10 YEAR WARRANTY

*With a core-strengthening ingredient of natural quarry stone crushed to a fine powder and then mixed with a powerful blend of latex and adhesives, **Coastal Armour by Quoizel** creates the next generation of products by using a material of extraordinary strength, durability and beauty.*

Our Coastal Armour composite material has been tested to withstand extreme heat and brutal cold; it is non-corrosive (acid and alkali-resistant) and UV resistant – both properties that make it stronger than the best resin products. That is why we are offering a 5 year warranty. Our unique synthetic composite formula allows us to fabricate our designs in high pressure injected steel molds that produce a superior quality of detail while increasing surface durability.

***Coastal Armour by Quoizel** will ensure many years of enjoyment with our beautiful outdoor products.*

INDOOR
OUTDOOR



SNNL1909PN DAMP



LED CHART

SNNL8406K	
Lumens	880
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

SNNL8406K WET

LED CHART

SNNL1909K/PN / SNNL8408K/PN SNNL8409K/PN / SNNL9009K/PN	
Lumens	1280
Total Watts	16W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No



SNNL8408K WET



WET **SNNL9009PN**

Stonington COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SNNL1909K/PN	15" H, 9.5" W, 9.5" Dp.	1" x 5.125"	-	See LED Chart
SNNL8406K/PN	10.5" H, 6.5" W, 7.5" Ext.	4.5" x 6.5"	3.5"	See LED Chart
SNNL8408K/PN	13" H, 8" W, 9.5" Ext.	4.5" x 6.5"	3.5"	See LED Chart
SNNL8409K/PN	15.5" H, 9.5" W, 10.5" Ext.	4.5" x 8"	4"	See LED Chart
SNNL9009K/PN	16.5" H, 9.5" W, 9.5" Ext.	-	-	See LED Chart

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Stonington COLLECTION

FINISH:

K Mystic Black **PN** Palladian Bronze **W** Fresco **NEW!**

GLASS:

Clear Water



by QUOIZEL

5 YEAR WARRANTY



WET SNN8409W

NEW!
FOR ♦ 2016



DAMP SNN1612W

NEW!
FOR ♦ 2016

TITLE 24 **DAMP** SNN1909PN

INDOOR
OUTDOOR



NEW!
FOR ♦ 2016



TITLE 24 **WET** SNN8406W

Available in 3 finishes!



SNN8408PN **WET** **TITLE 24**



TITLE 24 **WET** SNN9009K

Stonington COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SNN1612K/PN/W	6" H, 12" W, 12" Dp.	1" x 12"	-	2-60W Med. Base or 13W CFL
SNN1909K/PN/W	15" H, 9.5" W, 9.5" Dp.	1" x 5.125"	-	1-100W Med. Base or 23W CFL
SNN8406K/PN/W	10.5" H, 6.5" W, 7.5" Ext.	4.5" x 6.5"	3.5"	1-100W Med. Base or 23W CFL
SNN8408K/PN/W	13" H, 8" W, 9.5" Ext.	4.5" x 6.5"	2.5"	1-100W Med. Base or 23W CFL
SNN8409K/PN/W	15.5" H, 9.5" W, 10.5" Ext.	4.5" x 8"	2.5"	1-100W Med. Base or 23W CFL
SNN9009K/PN/W	16.5" H, 9.5" W, 9.5" Dp.	-	-	1-100W Med. Base or 23W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Cathedral COLLECTION

FINISH:
Palladian Bronze

GLASS:
Clear Seedy

NEW!
FOR ♦ 2016



by QUOIZEL

5 YEAR WARRANTY



CATL8411PN 



CATL1911PN **DAMP**

**INDOOR
OUTDOOR**



WET CATL8407PN

LED CHART

CATL8407PN	
Lumens	880
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

INTEGRATED LED
10 YEAR WARRANTY



LED CHART

CATL1911PN / CATL8409PN CATL8411PN / CATL9011PN	
Lumens	1280
Total Watts	16W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2700K
Dimmable	No

CATL8409PN **WET**



WET CATL9011PN

Cathedral COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	LIGHT SOURCE
CATL1911PN	18.5" H, 11.5" W, 8.5" Dp.	5.125"	-	See LED Chart
CATL8407PN	11" H, 7.5" W, 6.5" Dp.	4.75" x 6.5"	3.5"	See LED Chart
CATL8409PN	13.5" H, 9.5" W, 8" Dp.	4.75" x 8"	4"	See LED Chart
CATL8411PN	16.5" H, 11.5" W, 9.5" Dp.	4.75" x 8"	4"	See LED Chart
CATL9011PN	19" H, 11.5" W, 8.5" Dp.	-	-	See LED Chart

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Cathedral COLLECTION

FINISH:
Palladian Bronze

GLASS:
Clear Seedy

NEW!
FOR ♦ 2016



5 YEAR WARRANTY



CAT8411PN 



Cathedral COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
CAT1911PN	18.5" H, 11.5" W, 8.5" Dp.	5.125"	-	1-150W Med. Base or 40W CFL
CAT8407PN	11" H, 7.5" W, 6.5" Ext.	4.75" x 6.5"	3.5"	1-100W Med. Base or 23W CFL
CAT8409PN	13.5" H, 9.5" W, 8" Ext.	4.75" x 8"	4"	1-100W Med. Base or 23W CFL
CAT8411PN	16.5" H, 11.5" W, 9.5" Ext.	4.75" x 8"	4"	1-150W Med. Base or 40W CFL
CAT9011PN	19" H, 11.5" W, 8.5" Dp.	-	-	1-150W Med. Base or 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

FortQuinn COLLECTION

FINISH:

AW Antique Brown **MK** Marcado Black

GLASS:

Amber Seedy

FQ8414AW 





FQ8411AW 



FQ8407MK  



5 YEAR WARRANTY

  FQ8409MK



 FQ9011AW

FortQuinn COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
FQ8407AW/MK	15" H, 7" W, 9" Ext.	6.5" x 4.75"	6.5"	1-100W Med. Base or 23W CFL
FQ8409AW/MK	19" H, 9" W, 11.5" Ext.	8" x 4.75"	8.5"	1-100W Med. Base or 23W CFL
FQ8411AW/MK	23" H, 11" W, 14.5" Ext.	8" x 4.75"	11"	3-60W Cand. Base
FQ8414AW/MK*	30" H, 14" W, 18" Ext.	7.125" x 11"	15"	4-60W Cand. Base
FQ9011AW/MK	19" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base



*FQ8414AW/MK is not Coastal Armour and is not covered by the 5 Year Warranty.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

FortQuinn COLLECTION

FINISH:

Marcado Black

  FQ1931MK01



INDOOR
OUTDOOR

FQ1920MK01 



FortQuinn COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
FQ1920MK01*	41" H, 19" W, 19" Dp.	5"	4-60W Cand. Base
FQ1931MK01*	52" H, 31" W, 31" Dp.	5"	8-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

*FQ1920MK01 and FQ1931MK01 are not Coastal Armour and are not covered by the 5 Year Warranty.

OUTDOOR



From the **FORT QUINN COLLECTION:**
FQ8407MK

Bedford COLLECTION

FINISH:

K Mystic Black **PN** Palladian Bronze

GLASS:

Clear Seedy



5 YEAR WARRANTY



TITLE 24 WET BFD8410K



BFD1910K DAMP TITLE 24

**INDOOR
OUTDOOR**



TITLE 24 WET **BFD8407PN**



BFD8408K WET TITLE 24



TITLE 24 WET **BFD9010PN**

Bedford

COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
BFD1910K/PN	18" H, 10" W, 10" Dp.	5.25"	-	1-150W Med. Base or 40W CFL
BFD8407K/PN	13" H, 7" W, 8" Ext.	5.5" x 6.75"	3.75"	1-100W Med. Base or 23W CFL
BFD8408K/PN	15.5" H, 8.5" W, 9.5" Ext.	6.5" x 8"	3.75"	1-100W Med. Base or 23W CFL
BFD8410K/PN	18.5" H, 10" W, 11" Ext.	7.5" x 9.25"	4.25"	1-150W Med. Base or 40W CFL
BFD9010K/PN	19" H, 10" W, 10" Dp.	-	-	1-150W Med. Base or 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Tudor COLLECTION

FINISH:

K Mystic Black **PN** Palladian Bronze

GLASS:

Clear Seedy



5 YEAR WARRANTY



 **TDR8409PN**



TDR1909K DAMP TITLE 24

**INDOOR
OUTDOOR**



TDR8406PN WET TITLE 24



TDR8408PN WET TITLE 24



TITLE 24 WET **TDR9009PN**

Tudor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TDR1909K/PN	14.5" H, 9.5" W, 9.5" Dp.	5.12"	-	1-150W Med. Base or 40W CFL
TDR8406K/PN	10.5" H, 6.5" W, 7.5" Ext.	6.5" x 4.62"	2.75"	1-100W Med. Base or 23W CFL
TDR8408K/PN	12.5" H, 8" W, 9" Ext.	6.5" x 4.62"	2.75"	1-100W Med. Base or 23W CFL
TDR8409K/PN	15" H, 9.5" W, 10.5" Ext.	8" x 4.75"	2.75"	1-150W Med. Base or 40W CFL
TDR9009K/PN	16" H, 9.5" W, 9.5" Dp.	-	-	1-150W Med. Base or 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Marblehead COLLECTION

FINISH:

K Mystic Black **PN** Palladian Bronze

GLASS:

Clear Seedy



by QUOIZEL

5 YEAR WARRANTY

WET MBH8411K

Marblehead COLLECTION

PRODUCT

MBH8411K/PN

DIMENSIONS

17.5" H, 11" W, 12" Ext.

BACKPLATE

8" x 5.5"

HCWO

3.5"

BULBS

3-60W Cand. Base

OUTDOOR



From the **MARBLEHEAD COLLECTION:**
MBH8407PN

Marblehead COLLECTION

FINISH:

- K** Mystic Black
- PN** Palladian Bronze

GLASS:

Clear Seedy



TITLE 24 WET MBH8407PN



MBH1911PN DAMP

**INDOOR
OUTDOOR**



WET MBH9011K



by QUOIZEL

5 YEAR WARRANTY

MBH8409K WET

Marblehead COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MBH1911K/PN	18" H, 11" W, 11" Dp.	5"	-	3-60W Cand. Base
MBH8407K/PN	11" H, 7" W, 8" Ext.	6.5" x 4.5"	3"	1-100W Med. Base or 23W CFL
MBH8409K/PN	14.5" H, 9" W, 10" Ext.	8" x 5.5"	3.5"	3-60W Cand. Base
MBH9011K/PN	19" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Crestview COLLECTION

o u t d o o r

FINISH:
Western Bronze

GLASS:
Clear Seedy

NEW!
FOR ♦ 2016



  CVW8406WT



CVW8408WT  



CVW8407WT  



Crestview COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
CVW8406WT	12.5" H, 6" W, 5" Ext.	5" x 4.75"	4.75"	1-60W Vintage Bulb Supplied*
CVW8407WT	15.5" H, 7" W, 6" Ext.	6" x 6"	4.75"	1-60W Vintage Bulb Supplied*
CVW8408WT	18.5" H, 8" W, 6.5" Ext.	6" x 6"	6"	1-60W Vintage Bulb Supplied**

*Max. Wattage: 100W Med. Base or 23W CFL. **Max. Wattage: 150W Med. Base or 40W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Miles COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Water

NEW!
FOR ♦ 2016



MLS8407IB  



MLS1907IB **DAMP** **TITLE 24**

INDOOR
OUTDOOR



MLS8406IB **WET** **TITLE 24**



MLS8405IB **WET** **TITLE 24**



TITLE 24 **WET** **MLS9007IB**

Miles COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MLS1907IB	20" H, 7.5" W, 7.5" Dp.	4.5"	-	1-150W Medium Base or 40W CFL
MLS8405IB	16.5" H, 5.5" W, 7" Ext.	7" x 4.5"	6.5"	1-100W Med. Base or 23W CFL
MLS8406IB	19" H, 6.5" W, 8.5" Ext.	9" x 5"	8"	1-100W Med. Base or 23W CFL
MLS8407IB	21.5" H, 7.5" W, 9.5" Ext.	9" x 5"	8.5"	1-150W Medium Base or 40W CFL
MLS9007IB	19.5" H, 7.5" W, 7.5" Dp.	-	-	1-150W Medium Base or 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)


Booker COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Seedy

NEW!
FOR ♦ 2016

BKR8410K  





BKR1910K  



BKR8406K  

INDOOR
OUTDOOR



BKR8408K  



  **BKR9010K**

Booker COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
BKR1910K	18" H, 10.5" W, 9" Dp.	5"	-	1-60W Vintage Bulb Supplied**
BKR8406K	11.5" H, 7" W, 6.5" Ext.	7" x 4.5"	4.5"	1-60W Vintage Bulb Supplied*
BKR8408K	15" H, 9" W, 8.5" Ext.	7" x 4.5"	5.25"	1-60W Vintage Bulb Supplied*
BKR8410K	18.5" H, 11" W, 10" Ext.	7" x 4.5"	6.5"	1-60W Vintage Bulb Supplied**
BKR9010K	19.5" H, 10.5" W, 10.5" Dp.	-	-	1-60W Vintage Bulb Supplied**

Outdoor hanging fixtures come with 12' of wire and 8' of chain. *Max. Wattage: 100W Med. Base or 23W CFL. **Max. Wattage: 150W Med. Base or 40W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Hunter COLLECTION

FINISH:
imperial Bronze

GLASS:
Light Amber

HTR8408IB  





HTR1908IB **DAMP** **TITLE 24**



HTR8406IB **WET** **TITLE 24**



HTR8407IB **WET** **TITLE 24**



TITLE 24 **WET** HTR9008IB

Hunter COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
HTR1908IB	19" H, 8.5" W, 8.5" Dp.	5"	-	1-150W Med. Base or 40W CFL
HTR8406IB	11.5" H, 6" W, 7" Ext.	4.625" x 4.625"	2.5"	1-100W Med. Base or 23W CFL
HTR8407IB	15" H, 7.5" W, 8.5" Ext.	6" x 6"	3"	1-100W Med. Base or 23W CFL
HTR8408IB	18.5" H, 8.5" W, 9.5" Ext.	7.125" x 7.125"	3.5"	1-150W Med. Base or 40W CFL
HTR9008IB	21" H, 8.5" W, 8.5" Dp.	-	-	1-150W Med. Base or 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Oasis COLLECTION

FINISH:
Medici Bronze

GLASS:
Clear Beveled

WET OAS8413Z

S·O·L·I·D
BRASS





OAS1909Z **DAMP**



WET OAS8411Z

TITLE 24 **WET**

OAS8406Z

S·O·L·I·D
BRASS



OAS8408Z **WET**



OAS9011Z **WET**



OAS9009Z **WET**

WET OAS8409Z



OasisCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
OAS1909Z	20.5" H, 9" W, 9" Dp.	5"	-	3-60W Cand. Base
OAS8406Z	17" H, 5.5" W, 7.5" Ext.	6" x 4.5"	8.5"	1-100W Med. Base or 23W CFL
OAS8408Z	21" H, 7.5" W, 9" Ext.	6" x 4.5"	9.5"	2-60W Cand. Base
OAS8409Z	23" H, 9" W, 11" Ext.	6" x 4.5"	9.5"	3-60W Cand. Base
OAS8411Z	26" H, 11" W, 12.5" Ext.	8.25" x 5.375"	11"	4-60W Cand. Base
OAS8413Z	33" H, 14" W, 15.5" Ext.	10" x 6"	14"	5-60W Cand. Base
OAS9009Z	22" H, 9" W, 9" Dp.	-	-	3-60W Cand. Base
OAS9011Z	26.5" H, 11" W, 11" Dp.	-	-	4-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Harmony COLLECTION

FINISH:
imperial Bronze

GLASS:
Cream Linen



TITLE 24 WET

HY8413IB

TITLE 24

- CFL Spring Self-Ballasted GU 24

Not Shown:

HY8407IBFL
HY8507IBFL
1-23W CFL

HY8409IBFL
HY8509IBFL
1-23W CFL

HY8513IBFL
1-23W CFL

CAST
Aluminum



HY1911IB **DAMP**



HY8409IB **WET** **TITLE 24**

CAST
Aluminum



HY8407IB **WET** **TITLE 24**



WET HY9011IB

HY8411IB **WET**



Harmony COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
HY1911IB	20.5" H, 11" W, 11" Dp.	5"	-	3-60W Cand. Base
HY8407IB	10.5" H, 6.5" W, 8" Ext.	5" x 8.75"	2.38"	1-100W Med. Base or 23W CFL
HY8409IB	14" H, 9" W, 11" Ext.	5" x 11.25"	4.25"	1-150W Med. Base or 40W CFL
HY8411IB	17.5" H, 11" W, 13.5" Ext.	6" x 13.5"	4"	3-60W Cand. Base
HY8413IB	20.5" H, 13" W, 15.5" Ext.	6" x 13.5"	4"	1-150W Med. Base or 40W CFL
HY9011IB	20.5" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Hillcrest COLLECTION

FINISH:
imperial Bronze

GLASS:
Translucent Linen



TITLE
24

- CFL Spring Self-Ballasted
GU 24

Not Shown:

HC1109IBFL HC8413IBFL
HC1909IBFL HC8513IBFL
1-23W CFL 1-23W CFL

HC1913IBFL HC9011IBFL
1-23W CFL HC9111IBFL
1-23W CFL

HC8406IBFL HC9013IBFL
HC8506IBFL 1-23W CFL

HC8407IBFL HCE8409IBFL
HC8507IBFL HCE8509IBFL
1-23W CFL 1-23W CFL

HC8409IBFL HCE8411IBFL
HC8509IBFL HCE8511IBFL
1-23W CFL 1-23W CFL

HC8411IBFL
HC8511IBFL
1-23W CFL

HC8413IB WET TITLE 24

CAST
Aluminum



HC8409IB



HC8411IB



HC8407IB



HCE8411IB



HCE8409IB

CAST
Aluminum



HC8406IB

Hillcrest COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
HC8406IB	9.5" H, 6" W, 7" Ext.	4.5" x 4.5"	2.5"	1-100W Med. Base or 23W CFL
HC8407IB	10" H, 7" W, 8" Ext.	4.5" x 7"	2.5"	1-150W Med. Base or 40W CFL
HC8409IB	12.5" H, 9" W, 10" Ext.	4.5" x 7"	2.75"	1-150W Med. Base or 40W CFL
HC8411IB	15.5" H, 11" W, 12" Ext.	4.5" x 7"	2.75"	1-150W Med. Base or 40W CFL
HC8413IB	17.5" H, 13" W, 14" Ext.	4.5" x 10"	2.75"	1-150W Med. Base or 40W CFL
HCE8409IB	20" H, 9" W, 10" Ext.	5" x 13"	6.5"	1-150W Med. Base or 40W CFL
HCE8411IB	25.5" H, 11" W, 12" Ext.	5" x 16"	8"	1-150W Med. Base or 40W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)



From the **HILLCREST COLLECTION**
Wall Lantern: **HC8413IB**

Hillcrest COLLECTION

OUTDOOR

FINISH:
imperial Bronze

GLASS:
Translucent Linen



HC1909IB



HC1612IB

CAST
Aluminum



HC1913IB



HC9011IB



HC9013IB

Hillcrest COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
HC1612IB	7" H, 11.5" W, 11.5" Dp.	-	2-60W Med. Base or 13W CFL
HC1909IB	13" H, 9" W, 9" Dp.	4.5"	1-150W Med. Base or 40W CFL
HC1913IB	18" H, 13" W, 13" Dp.	4.5" x 4.5"	1-150W Med. Base or 40W CFL
HC9011IB	19" H, 11" W, 11" Dp.	-	1-150W Med. Base or 40W CFL
HC9013IB	19.5" H, 13" W, 13" Dp.	-	1-150W Med. Base or 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Lodge COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Hammered



ETL E24 WET LDG8409K



LDG8406K   



  **LDG8408K**



  **LDG9009K**

  **LDG1909K**



LodgeCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
LDG1909K	13.5" H, 9.5" W, 9.5" Dp.	5.12"	-	1-100W Med. Base or 23W CFL
LDG8406K	9" H, 6.5" W, 7.5" Ext.	4.37" x 4.37"	3.5"	1-100W Med. Base or 23W CFL
LDG8408K	10.5" H, 8" W, 9" Ext.	4.37" x 4.37"	3.5"	1-100W Med. Base or 23W CFL
LDG8409K	12.5" H, 9.5" W, 10.5" Ext.	6.5" x 4.5"	5"	1-100W Med. Base or 23W CFL
LDG9009K	16" H, 9.5" W, 9.5" Dp.	-	-	1-100W Med. Base or 23W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Millhouse COLLECTION

FINISH:

K Mystic Black **VN** Veneto **NEW!**

GLASS:

Clear Seedy

NEW!

FOR ♦ 2016

MHE8410VN **WET**





MHE1910K DAMP



MHE8406VN WET TITLE 24

NEW!
FOR ♦ 2016



WET MHE8409VN

NEW!
FOR ♦ 2016



WET MHE9010K

Millhouse COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MHE1910K/VN	19" H, 10" W, 10" Dp.	5"	-	3-60W Cand. Base
MHE8406K/VN	15.5" H, 7" W, 7.5" Ext.	4.5" x 6"	6"	1-100W Med. Base or 23W CFL
MHE8409K/VN	18.5" H, 8" W, 8.5" Ext.	4.5" x 6"	8"	2-60W Cand. Base
MHE8410K/VN	22" H, 10" W, 10.5" Ext.	8" x 5"	9.5"	3-60W Cand. Base
MHE9010K/VN	21.5" H, 10" W, 10" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)



The Charleston Copper Lantern Collection gives you the historic look of gas lighting. Charleston Copper Lanterns are all electric, solid copper and hand riveted giving your home the romantic, reproduction style of antique gas lights still popular today on many of the charming homes in Charleston and New Orleans.

From the **RUE DE ROYAL COLLECTION**
Wall Lantern: **R08414AC** 

Rue de Royale COLLECTION

OUTDOOR

FINISH:
Aged Copper

GLASS:
Clear

WET RO8311AC

RO1914AC **DAMP**

RO8411AC **WET**

S·O·L·I·D
COPPER

WET RO9014AC

RO8410AC **WET** **TITLE 24**

Rue de Royal COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
RO1914AC	29.5" H, 27.5" W, 27.5" Dp.	5"	-	4-60W Cand. Base
RO8311AC	23.5" H, 10.5" W, 13" Ext.	5" x 5"	10.5"	2-60W Cand. Base
RO8410AC	20.5" H, 9.5" W, 11" Ext.	5" x 5"	10.5"	1-100W Med. Base or 23W CFL
RO8411AC	22" H, 10.5" W, 13" Ext.	5" x 5"	10.5"	2-60W Cand. Base
RO8414AC	29" H, 13.5" W, 16" Ext.	5" x 5"	14"	4-60W Cand. Base
RO9014AC	26" H, 17" W, 15.5" Dp.	-	-	4-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Outdoor exposure will naturally darken the hue of copper products over time.

Chalmers COLLECTION

FINISH:
Aged Copper

GLASS:
Clear

TITLE 24 WET CM8408AC



DAMP CM1912AC



S·O·L·I·D
COPPER

WET CM9012AC



WET CM8412AC



Chalmers COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
CM1912AC	26" H, 12" W, 12" Dp.	5.5"	-	3-60W Cand. Base
CM8408AC	15.5" H, 8" W, 9" Ext.	8" x 5.5"	8"	1-100W Med. Base or 23W CFL
CM8410AC	19" H, 10" W, 11.5" Ext.	8" x 5.5"	8"	2-60W Cand. Base
CM8412AC	23" H, 12" W, 13.5" Ext.	8" x 5.5"	11"	3-60W Cand. Base
CM9012AC	26" H, 12" W, 12" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Outdoor exposure will naturally darken the hue of copper products over time.

OUTDOOR



The Charleston Copper Lantern Collection gives you the historic look of gas lighting. Charleston Copper Lanterns are all electric, solid copper and hand riveted giving your home the romantic, reproduction style of antique gas lights still popular today on many of the charming homes in Charleston and New Orleans.

From the **CHALMERS COLLECTION**
Wall Lantern: CM8410AC 

Cooper COLLECTION

FINISH:

CU Copper Bronze **K** Mystic Black

GLASS:

Clear Seedy



COR8412K **WET** **24**

TITLE 24 DAMP COR1611K



COR1611CU DAMP TITLE 24

COR8409K WET TITLE 24



COR8410K WET TITLE 24



TITLE 24 WET COR9010K



Cooper COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
COR1611CU/K	10.5" H, 11.5" W, 11.5" Dp.	1" x 7"	-	1-100W Med. Base or 23W CFL
COR8409K	17.5" H, 9" W, 11" Ext.	4" x 5.5"	12"	1-100W Med. Base or 23W CFL
COR8410K	21" H, 10" W, 12" Ext.	4.5" x 7"	13"	1-100W Med. Base or 23W CFL
COR8412K	24.5" H, 12" W, 13" Ext.	4.5" x 8.5"	13"	1-150W Med. Base or 40W CFL
COR9010K	18" H, 10" W, 10" Dp.	-	-	1-100W Med. Base or 23W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)


Marine COLLECTION

FINISH:
Western Bronze

GLASS:
Clear Seedy



VINTAGE STYLE
bulb included



WET MRE8410WT



MRE1909WT **DAMP** **TITLE 24**



MRE1506WT **DAMP**

INDOOR
OUTDOOR

TITLE 24 **WET** MRE8406WT



TITLE 24 **WET** MRE8409WT



MRE8408WT **WET** **TITLE 24**



TITLE 24 **WET** MRE9009WT

MarineCOLLECTION

PRODUCT .	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MRE1506WT	12" H*, 6" W, 6" Dp.	6"	-	1-60W Vintage Bulbs Supplied†
MRE1909WT	20" H, 9.5" W, 9.5" Dp.	.75" x 6"	-	1-60W Vintage Bulbs Supplied†
MRE8406WT	11.5" H, 6.5" W, 7" Ext.	5" x 6.37"	4"	1-60W Vintage Bulbs Supplied†
MRE8408WT	15" H, 8.5" W, 9" Ext.	4.75" x 9"	5"	1-60W Vintage Bulbs Supplied†
MRE8409WT	17" H, 9.5" W, 11" Ext.	4.75" x 9"	5.5"	1-60W Vintage Bulbs Supplied†
MRE8410WT	20" H, 11" W, 11.5" Ext.	9" x 4.75"	5.5"	3-40W Vintage Bulbs Supplied††
MRE9009WT	23" H, 11" W, 11" Dp.	-	-	1-60W Vintage Bulbs Supplied†

Outdoor hanging fixtures come with 12' of wire and 8' of chain. *Comes with (2) 6" and (2) 12" rods. †Max. Wattage: 100W Med. Base or 23W CFL. ††Max. Wattage: 60W Cand. Base.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Devon COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Beveled



CAST
Aluminum

DE8961IB 



DE1490IB DAMP



WET DE8959IB



WET DE8960IB



WET DE9256IB



DE8976IB WET



TITLE 24 WET DE8958IB

Devon COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
DE1490IB	31" H, 11" W, 11" Dp.	5.5"		3-60W Cand. Base
DE8958IB	12.5" H, 7" W, 8.5" Ext.	4.75" x 7.75"	4"	1-150W Med. Base or 40W CFL
DE8959IB	21" H, 9" W, 11" Ext.	5" x 10"	14"	2-60W Cand. Base
DE8960IB	26" H, 11" W, 14" Ext.	5" x 12"	17.5"	3-60W Cand. Base
DE8961IB	25" H, 11" W, 14" Ext.	5" x 12"	4"	3-60W Cand. Base
DE8976IB	21" H, 9" W, 11" Ext.	5" x 10"	5"	2-60W Cand. Base
DE9256IB	23" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Ridge COLLECTION

FINISH:
Western Bronze

GLASS:
Clear

RGE8411WT  

CAST
Aluminum





RGE1911WT  

**INDOOR
OUTDOOR**



  RGE8407WT



  RGE8409WT



  RGE9011WT

Ridge COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
RGE1911WT	19" H, 11" W, 9.5" Dp.	4.375"	-	1-60W Vintage Bulb Supplied*
RGE8407WT	12.5" H, 7" W, 7" Ext.	6.5" x 4.5"	3.5"	1-60W Vintage Bulb Supplied**
RGE8409WT	16" H, 9" W, 8.5" Ext.	7" x 4.5"	5.5"	1-60W Vintage Bulb Supplied**
RGE8411WT	19" H, 11" W, 10.5" Ext.	9" x 5"	5.5"	1-60W Vintage Bulb Supplied*
RGE9011WT	21.5" H, 11" W, 9.5" Dp.	-	-	1-60W Vintage Bulb Supplied*

Outdoor hanging fixtures come with 12' of wire and 8' of chain. *Max Wattage: 100W Med. Base or 25W CFL. **Max Wattage: 150W Med. Base or 40W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Rutledge COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Beveled

S·O·L·I·D
BRASS



WET RJ8414K



RJ1911K **DAMP**

**INDOOR
OUTDOOR**



TITLE 24 **WET** RJ8407K



WET RJ8409K



RJ8411K **WET**



WET RJ9011K

Rutledge COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
RJ1911K	19.5" H, 11" W, 11" Dp.	5"	-	3-60W Cand. Base
RJ8407K	15" H, 7" W, 8.5" Ext.	4.75" x 7"	7"	1-150W Med. Base or 40W CFL
RJ8409K	19" H, 9" W, 10" Ext.	4.75" x 7"	9"	2-60W Cand. Base
RJ8411K	24" H, 11" W, 12.5" Ext.	5" x 9.5"	11.5"	3-60W Cand. Base
RJ8414K	29" H, 13.5" W, 15.5" Ext.	5" x 12.5"	14.5"	4-60W Cand. Base
RJ9011K	20.5" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Byron COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Beveled



BRN8412IB  



BRN1910IB DAMP TITLE 24

**INDOOR
OUTDOOR**



TITLE 24 WET **BRN8406IB**



TITLE 24 WET **BRN8408IB**



BRN8410IB WET TITLE 24



TITLE 24 WET **BRN9010IB**

Byron COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
BRN1910IB	20.5" H, 10" W, 7" Dp.	4.5" x 4.5"	-	1-60W Vintage Bulb Supplied*
BRN8406IB	12" H, 6.5" W, 5.5" Ext.	5.75" x 4"	3"	1-60W Vintage Bulb Supplied*
BRN8408IB	14.5" H, 8" W, 7" Ext.	6.5" x 4"	3.5"	1-60W Vintage Bulb Supplied*
BRN8410IB	18" H, 10" W, 8.5" Ext.	9" x 5"	5"	1-60W Vintage Bulb Supplied*
BRN8412IB	21.5" H, 12" W, 8.5" Ext.	9" x 5"	15"	2-60W Vintage Bulbs Supplied*
BRN9010IB	21" H, 10" W, 10" Dp.	3.25"	-	1-60W Vintage Bulb Supplied*

Outdoor hanging fixtures come with 12' of wire and 8' of chain. *Max Wattage: 100W Med. Base or 23W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Steadman COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Seedy

CAST
Aluminum

VINTAGE STYLE
bulb included



TITLE 24 WET SDN8409IB



SDN1908IB DAMP TITLE 24

**INDOOR
OUTDOOR**



DAMP **SDN1506IB**

TITLE 24 WET **SDN8407IB**



WET TITLE 24 **SDN8408IB**



SDN8405IB WET TITLE 24



TITLE 24 WET **SDN9008IB**

Steadman COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SDN1506IB	12" H*, 5.5" W, 5.5" Dp.	5"	-	1-60W Vintage Bulb Supplied**
SDN1908IB	21" H, 8.5" W, 8.5" Dp.	5"	-	1-60W Vintage Bulb Supplied**
SDN8405IB	12.5" H, 6" W, 7" Ext.	5.5" x 5.5"	4.75"	1-60W Vintage Bulb Supplied**
SDN8407IB	16" H, 7" W, 8.5" Ext.	6.5" x 6.5"	6"	1-60W Vintage Bulb Supplied**
SDN8408IB	19.5" H, 8" W, 10.5" Ext.	6.5" x 6.5"	7.5"	1-60W Vintage Bulb Supplied**
SDN8409IB	23" H, 10" W, 11.5" Ext.	8.5" x 8.5"	9"	2-60W Vintage Bulbs Supplied**
SDN9008IB	20.5" H, 8.5" W, 11.5" Dp.	-	-	1-60W Vintage Bulb Supplied**

Chain-hung fixture comes with 12' of wire and 8' of chain. *Comes with (2) 6" and (2) 12" rods. **Max Wattage: 100W Med. Base or 23W CFL.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Galen COLLECTION

FINISH:
imperial Bronze

GLASS:
umber linen

CAST
Aluminum



TITLE 24 WET **GLN8412IB**

Galen COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
GLN8412IB	14.5" H, 11.5" W, 10" Ext.	7" x 4.5"	4"	1-150W Med. Base or 40W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

o u t d o o r



From the **GALEN COLLECTION**
GLN8409IB

Galen COLLECTION

FINISH:
imperial Bronze

GLASS:
umber Linen

  **GLN1910IB**



GLN8409IB  



**INDOOR
OUTDOOR**



  **GLN8407IB**

CAST
Aluminum



  **GLN8410IB**

Enlarged for detail



GLN9010IB  

Galen COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
GLN1910IB	13.5" H, 10" W, 10" Dp.	4.5" x 4.5"	-	1-150W Med. Base or 40W CFL
GLN8407IB	7.5" H, 6.5" W, 6" Dp.	5.5" x 4.5"	2.75"	1-100W Med. Base or 23W CFL
GLN8409IB	10" H, 8.5" W, 7.5" Ext.	7" x 4.5"	3.5"	1-150W Med. Base or 40W CFL
GLN8410IB	12" H, 10" W, 8.5" Dp.	7" x 4.5"	3.5"	1-150W Med. Base or 40W CFL
GLN9010IB	15" H, 10" W, 10" Dp.	-	-	1-150W Med. Base or 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Chancellor COLLECTION

o u t d o o r

FINISH:
Copper Bronze

GLASS:
Clear

 **CCR8406CU**



CCR8408CU 



 **CCR8410CU**



CCR9010CU 



Chancellor COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
CCR8406CU	11.5" H, 5.5" W, 6.5" Ext.	5" x 4"	4"	1-100W Med. Base or 23W CFL
CCR8408CU	19" H, 8" W, 9" Ext.	6" x 5"	7.5"	2-60W Cand. Base
CCR8410CU	23.5" H, 11" W, 11" Ext.	7.5" x 5.5"	11"	3-60W Cand. Base
CCR9010CU	22" H, 10" W, 10" Dp.	-	-	3-60W Cand. Base

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Trumbull COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Seedy

WET TML8408K





TML1908K DAMP

**INDOOR
OUTDOOR**



TML8405K WET



TML8407K WET



WET **TML9008K**

Trumbull COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TML1908K	19" H, 8.5" W, 8.5" Dp.	1" x 5"		3-60W Cand. Base
TML8405K	14.5" H, 5.5" W, 6" Ext.	4.5" x 4.5"	9.5"	1-60W Cand. Base
TML8407K	18.5" H, 7" W, 8" Ext.	5" x 5"	12.5"	2-60W Cand. Base
TML8408K	22.5" H, 8.5" W, 9.5" Ext.	5.5" x 5.5"	15"	2-60W Cand. Base
TML9008K	21.5" H, 8.5" W, 8.5" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

Province COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Seedy

CAST
Aluminum

PRV8409K WET





PRV1909K DAMP

INDOOR
OUTDOOR



PRV8406K WET TITLE 24



PRV8408K WET



WET PRV9009K

Province COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
PRV1909K	15.5" H, 9.5" W, 9.5" Dp.	4.5"	-	3-60W Cand. Base
PRV8406K	15.5" H, 6.5" W, 8" Ext.	6.5" x 4.5"	6.75"	1-100W Med. Base or 23W CFL
PRV8408K	17.5" H, 8.5" W, 9.5" Ext.	6.5" x 4.5"	7.5"	2-60W Cand. Base
PRV8409K	19" H, 9.5" W, 10.5" Ext.	7" x 4.5"	7.5"	3-60W Cand. Base
PRV9009K	18" H, 9.5" W, 9.5" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Powell COLLECTION

FINISH:
Western Bronze

GLASS:
White Art



TITLE 24 WET PWL8311WT



PWL8307WT  



PWL8309WT  



  **PWL1613WT**



  **PWL9009WT**

Powell COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
PWL1613WT	6" H, 13" W, 13" Dp.	9" x 5"	-	3-75W Med. Base or 18W CFL
PWL8307WT	13.5" H, 7" W, 5" Ext.	9" x 5"	8"	1-100W Med. Base or 23W CFL
PWL8309WT	17" H, 9" W, 5.5" Ext.	9" x 5"	11"	1-150W Med. Base or 40W CFL
PWL8311WT	20.5" H, 11" W, 6.5" Ext.	11" x 5"	13"	1-150W Med. Base or 40W CFL
PWL9009WT	20.5" H, 4.5" W, 9" Dp.	-	-	1-150W Med. Base or 40W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)



From the **BAIN COLLECTION**:
Wall Lantern: **BAN8411K**

Bain COLLECTION

o u t d o o r

FINISH:
Mystic Black

GLASS:
Clear Beveled

S·O·L·I·D
BRASS

WET BAN8411K



Bain COLLECTION

PRODUCT
BAN8411K

DIMENSIONS
22" H, 11" W, 10" Ext.

BACKPLATE
7" x 4.75"

HCWO
7.75"

BULBS
3-60W Cand. Base

Bain COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Beveled



TITLE 24 WET BAN8407K

DAMP BAN1911K

**INDOOR
OUTDOOR**



S·O·L·I·D
BRASS



BAN9011K WET

WET BAN8409K



Bain COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
BAN1911K	20.5" H, 11.5" W, 11.5" Dp.	5"	-	3-60W Cand. Base
BAN8407K	15" H, 7.5" W, 7" Ext.	5.75" x 4.5"	6.5"	1-100W Med. Base or 23W CFL
BAN8409K	18" H, 9.5" W, 8.5" Ext.	7" x 4.75"	7.5"	2-60W Cand. Base
BAN9011K	23" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Seaford COLLECTION

o u t d o o r

FINISH: imperial Bronze



SFD8407IB

SFD1911IB

SFD8409IB



SFD8411IB



**INDOOR
OUTDOOR**

Seaford COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SFD1911IB	8" H*, 11" W, 11" Dp.	5.75"	-	1-100W Med. Base or 23W CFL
SFD8407IB	8.5" H, 7" W, 8.5" Ext.	5.75" x 5.75"	4"	1-100W Med. Base or 23W CFL
SFD8409IB	9" H, 9" W, 10.5" Ext.	5.75" x 5.75"	5"	1-100W Med. Base or 23W CFL
SFD8411IB	11" H, 11" W, 12.5" Ext.	5.75" x 5.75"	5"	1-100W Med. Base or 23W CFL

Rod-hung fixtures come with 12' of wire. *Comes with (2) 6" and (2) 12" Rods.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Grover COLLECTION

FINISH:
Mystic Black

GLASS:
Clear Water

CAST
Aluminum



TITLE 24 WET GVR8410K



GVR1910K DAMP TITLE 24

**INDOOR
OUTDOOR**



TITLE 24 WET **GVR8406K**

CAST
Aluminum



GVR8408K WET TITLE 24



TITLE 24 WET **GVR9010K**

Grover COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
GVR1910K	17.5" H, 10.5" W, 10.5" Dp.	4.5"	-	1-150W Med. Base or 40W CFL
GVR8406K	11" H, 6.5" W, 7.5" Ext.	6.5" x 4.5"	4.5"	1-100W Med. Base or 23W CFL
GVR8408K	14.5" H, 8.5" W, 9.5" Ext.	6.5" x 4.5"	5"	1-100W Med. Base or 23W CFL
GVR8410K	17.5" H, 10.5" W, 11.5" Ext.	7.5" x 4.5"	5.75"	1-150W Med. Base or 40W CFL
GVR9010K	20.5" H, 10.5" W, 10.5" Dp.	-	-	1-150W Med. Base or 40W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Georgetown COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Beveled

CAST
Aluminum

GT8982IB WET





GT1700IB DAMP

**INDOOR
OUTDOOR**



TITLE 24 WET **GT8980IB**



WET **GT8981IB**

WET **GT9294IB**



Georgetown COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
GT1700IB	17" H, 10" W, 10" Dp.	5.5"	-	3-60W Cand. Base
GT8980IB	13" H, 7.5" W, 9" Ext.	5" x 7.5"	4"	1-150W Med. Base or 40W CFL
GT8981IB	18" H, 10" W, 11.5" Ext.	5.25" x 10.5"	8.5"	3-60W Cand. Base
GT8982IB	24" H, 13" W, 15" Ext.	5.75" x 13"	7"	4-60W Cand. Base
GT9294IB	19" H, 11" W, 11" Dp.	-	-	3-60W Cand. Base

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Chimera COLLECTION

FINISH:
imperial Bronze

GLASS:
Clear Water

CHI84131B 

CAST
Aluminum





CHI1911IB DAMP TITLE 24

**INDOOR
OUTDOOR**



TITLE 24 WET **CHI8407IB**



CHI8409IB WET TITLE 24



CHI8411IB WET TITLE 24



TITLE 24 WET **CHI9011IB**

Chimera COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
CHI1911IB	19" H, 11" W, 11" Dp.	5"	-	1-100W Med. Base or 23W CFL
CHI8407IB	15.5" H, 7" W, 9.5" Ext.	4.5" x 6.5"	6"	1-100W Med. Base or 23W CFL
CHI8409IB	19.5" H, 9" W, 11.5" Ext.	5" x 7.5"	6"	1-100W Med. Base or 23W CFL
CHI8411IB	22.5" H, 11" W, 13.5" Ext.	5" x 7.5"	7.5"	1-100W Med. Base or 23W CFL
CHI8413IB	28" H, 13" W, 16" Ext.	11" x 7"	11"	4-60W Cand. Base
CHI9011IB	21.5" H, 10.5" W, 10.5" Dp.	-	-	1-100W Med. Base or 23W CFL

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)



Milan

FINISH: Mystic Black
SHADE: opal etched

MLN8309K  

  **MLN8307K**



Milan COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
MLN8307K	14" H, 7" W, 4.5" Ext.	13" x 4.5"	5"	1-100W Med. Base or 23W CFL
MLN8309K	16.5" H, 9" W, 5.5" Ext.	15.5" x 5.75"	7"	1-100W Med. Base or 23W CFL

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo. (Medium base bulbs only)

Outdoor Lighting

Please see referenced page numbers for larger images and full descriptions of these products.

New England

NA8409PN
See page 119



New England

NA8414PN
See page 119



Zephyr

ZP8414MD
See page 240



Zephyr

ZP8418MD
See page 240



TIFFANY | QUOIZEL



From the **HYACINTH COLLECTION** (p.487)

TF1438VB


Photo courtesy of Enmark Construction Ltd.

Glass color in Tiffany lighting products may vary from images shown.

Shade colors will appear darker when not illuminated.

Victory COLLECTION

FINISH:
Valiant Bronze



detail



DAMP TFVY1716VA



NEW!


FOR ♦ 2016

TFVY2819VA DAMP

DAMP TFVY1404VA



All Quoizel Track Lights Swivel



TFVY9359VA 



TFVY6325VA 

NEW!
FOR ♦ 2016



 TFVY6118VA

Enlarged for detail

Victory COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFVY1404VA	15" H, 43" W, 6" Dp.	6"	4-100W Med. Base or 23W CFL	Contains 65 Pieces of Tiffany Glass
TFVY1716VA	13" H, 16" W, 16" Dp.	6"	2-75W Med. Base or 18W CFL	Contains 144 Pieces of Tiffany Glass
TFVY2819VA	23.5" H, 19.5" W, 19.5" Dp.	5.25"	3-100W Med. Base or 23W CFL	Contains 144 Pieces of Tiffany Glass
TFVY6118VA	19" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 192 Pieces of Tiffany Glass
TFVY6325VA	25.5" H, 18" W, 18" Dp.	-	2-100W Med. Base or 23W CFL	Contains 192 Pieces of Tiffany Glass
TFVY9359VA	59" H, 18" W, 18" Dp.	-	2-100W Med. Base or 23W CFL	Contains 192 Pieces of Tiffany Glass

All chain-hung fixtures come with 8' of wire and 4' of chain.

Alcott COLLECTION

FINISH:
Valiant Bronze

DAMP TFAT1716VA



DAMP TFAT2821VA



NEW!


FOR ♦ 2016

DAMP TFAT1507VA





TFAT9362VA 



detail



TFAT6325VA 

Enlarged for detail

Alcott COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFAT1507VA	10.5" H*, 7" W, 7" Dp.	2" x 5.5"	1-100W Med. Base or 23W CFL	Contains 112 Pieces of Tiffany Glass
TFAT1716VA	15.5" H, 16" W, 16" Dp.	1" x 5.5"	2-100W Med. Base or 23W CFL	Contains 240 Pieces of Tiffany Glass
TFAT2821VA	25.5" H, 22" W, 22" Dp.	2.5" x 7.75"	3-100W Med. Base or 23W CFL	Contains 320 Pieces of Tiffany Glass
TFAT6325VA	25" H, 19.5" W, 19.5" Dp.	-	2-75W Med. Base or 18W CFL	Contains 320 Pieces of Tiffany Glass
TFAT9362VA	62" H, 20.5" W, 20.5" Dp.	-	2-100W Med. Base or 23W CFL	Contains 320 Pieces of Tiffany Glass

All chain-hung fixtures come with 8' of wire and 4' of chain. *Comes with (2) 12" and (2) 6" Rods.

Englenook COLLECTION

FINISH:

Valiant Bronze

DAMP **TFIK1817VA**




DAMP **TFIK2817VA**



TFIK348VA

TFIK1508VA DAMP

Enlarged for detail



TFIK1714VA DAMP



TFIK1404VA DAMP



All Quoizel Track Lights Swivel

Inglenook COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFIK1404VA	14" H, 42" W, 6" Dp.	0.75" x 4.5"	4-100W Med. Base or 23W CFL	Each Shade Contains 184 Pieces of Tiffany Glass
TFIK1508VA	7" H*, 8" W, 8" Dp.	5.5"	1-100W Med. Base or 23W CFL	Contains 208 Pieces of Tiffany Glass
TFIK1714VA	8" H, 14" W, 14" Dp.	6.5"	2-60W Med. Base or 13W CFL	Contains 248 Pieces of Tiffany Glass
TFIK1817VA	12.5" H, 17" W, 17" Dp.	8"	3-100W Med. Base or 23W CFL	Contains 248 Pieces of Tiffany Glass
TFIK2817VA	25.5" H, 17.5" W, 17.5" Dp.	7"	3-100W Med. Base or 23W CFL	Contains 248 Pieces of Tiffany Glass
TFIK348VA	17.5" H, 47.5" W, 16" Dp.	8" x 4.5"	3-100W Med. Base or 23W CFL	Contains 496 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

Rod-hung fixture comes with 10' of wire. * Comes with (2) 6" and (2) 12" Rods.

nglenook COLLECTION

FINISH:

Valiant Bronze



TFF16191A5VA 



TFIK9471VA 



TFT16191A1VA 

Enlarged for detail

nglenook COLLECTION

PRODUCT	DIMENSIONS	BULBS	
TFF16191A5VA	62" H, 17" W, 17" Dp.	2-75W Med. Base or 18W CFL	Contains 260 Pieces of Tiffany Glass
TFIK9471VA	71" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	Contains 249 Pieces of Tiffany Glass
TFT16191A1VA	25" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 248 Pieces of Tiffany Glass



From the **INGLENOOK COLLECTION:**
TFIK2817VA (p. 464)

Englenook COLLECTION

FINISH:

Valiant Bronze

TFIK1617VA



TFIK8802



TFIK1509VA

NEW!
FOR ♦ 2016



TFIK6111VA



Englenook COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS	
TFIK1509VA	14" H*, 8.5" W, 8.5" Dp.	1.25" x 6"	-	1-100W Med. Base or 23W CFL	Contains 37 Pieces of Tiffany Glass
TFIK1617VA	6" H, 16.5" W, 16.5" Dp.	1" x 7"	-	2-75W Med. Base or 18W CFL	Contains 253 Pieces of Tiffany Glass
TFIK6111VA	11" H, 8.5" W, 8.5" Dp	-	-	1-60W Med. Base or 13W CFL	Contains 37 Pieces of Tiffany Glass
TFIK8802	7" H, 16" W, 5.5" Ext.	-	3"	2-60W Cand. Base	Contains 110 Pieces of Tiffany Glass

Rod-hung fixtures come with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Carroll COLLECTION

t I F F A N Y

FINISH:
Vintage Bronze



TF1508VB DAMP



DAMP **TF1805SVB**

Enlarged for detail

NEW!
FOR ♦ 2016

DAMP **TF1714VB**

Enlarged for detail



Carroll COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1508VB	7" H*, 8" W, 8" Dp.	2.75" x 7"	1-100W Med. Base or 23W CFL	Contains 214 Pieces of Tiffany Glass
TF1714VB	16" H, 14.5" W, 14.5" Dp.	6.5"	2-100W Med. Base or 23W CFL	Contains 417 Pieces of Tiffany Glass
TF1805SVB	7" H, 17" W, 17" Dp.	7"	2-75W Med. Base or 18W CFL	Contains 215 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

Asheville COLLECTION

FINISH:

Valiant Bronze

DAMP TFAS1615VA



The Asheville Tiffany Collection is a perfect example of understated elegance and class.



DAMP TFAS5003VA





TFAS2817VA DAMP



DAMP TFAS1507VA

DAMP TFAS344VA



Asheville COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFAS1507VA	11.5" H*, 7" W, 7" Dp.	5"	1-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS1615VA	6.5" H, 15" W, 15" Dp.	-	2-60W Med. Base or 13W CFL	Contains 60 Pieces of Tiffany Glass
TFAS2817VA	23" H, 17" W, 17" Dp.	5"	3-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS344VA	29" H, 44" W, 19" Dp.	1" x 4.5"	3-100W Med. Base or 23W CFL	Contains 316 Pieces of Tiffany Glass
TFAS5003VA	22.5" H, 23" W, 23" Dp.	5"	3-100W Med. Base or 23W CFL	Each Shade Contains 44 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

Asheville COLLECTION

FINISH:

Valiant Bronze

DAMP TFAS1714VA



TF1180TVA 



DAMP TFAS1404VA

All Quoizel Track Lights Swivel

Asheville COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1180TVA	25" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 44 Pieces of Tiffany Glass
TFAS1404VA	13.5" H*, 43.5" W, 7" Dp.	1.75" x 5.5"	4-100W Med. Base or 23W CFL	Each Shade Contains 44 Pieces of Tiffany Glass
TFAS1714VA	12" H, 14" W, 14" Dp	5.5"	2-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass

*Comes with (2) 6" and (2) 12" Rods.



From the **ASHEVILLE COLLECTION:**
TF-1180TVA

Asheville COLLECTION

FINISH:
Valiant Bronze

NEW!

FOR ♦ 2016

DAMP TFAS1817VA



DAMP TFAS9360VA



DAMP TFAS9470VA



NEW!

FOR ♦ 2016

Asheville COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFAS1817VA	17.5" H, 17" W, 17" Dp.	5.5"	3-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS9360VA	60" H, 17" W, 17" Dp.	-	2-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS9470VA	70.5" H, 12" W, 12" Dp.	-	1-150W Med. Base or 40W CFL	Contains 52 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

Larissa COLLECTION

t i F F A n Y



 **TF879T**



 **TF879F**

Larissa COLLECTION

PRODUCT	DIMENSIONS	BULBS	
TF879F	62" H, 18" W, 18" Dp.	2-100W Med. Base or 23W CFL	Contains 426 Pieces of Tiffany Glass
TF879T	22.5" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 426 Pieces of Tiffany Glass

Kami COLLECTION

FINISH:

Vintage Bronze


DAMP TFKM5103VB





DECORATIVE CHAIN

TFKM2840VB



TFKM1508VB

TF878CVB



PULL CHAIN

Kami COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF878CVB†	10.5" H, 20" W, 20" Dp.	5.5"	3-100W Med. Base or 23W CFL	Contains 360 Pieces of Tiffany Glass
TFKM1508VB	8.5" H*, 8" W, 8" Dp.	5.5"	1-100W Med. Base or 23W CFL	Contains 159 Pieces of Tiffany Glass
TFKM2840VB††	33.5" H, 40" W, 40" Dp.	5.25"	8-100W Med. Base or 23W CFL	Contains 532 Pieces of Tiffany Glass
TFKM5103VB†	22.5" H, 24.5" W, 24.5" Dp.	5.125"	3-100W Med. Base or 23W CFL	Each Shade Contains 159 Pieces of Tiffany Glass

†Chain-hung fixtures come with 8' of wire and 4' of chain. ††Chain-hung fixture comes with 12' of wire and 8' of chain. Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods.

KamiCOLLECTION

FINISH:
VB Vintage Bronze

TF1396SVB



TF878T

Enlarged for detail



TF878F

TF878UVB



KamiCOLLECTION

PRODUCT	DIMENSIONS	BULBS	
TF1396SVB	6" H, 17" W, 17" Dp.	2-75W Med. Base or 18W CFL	Contains 367 Pieces of Tiffany Glass
TF878F	62" H, 18" W, 18" Dp.	2-100W Med. Base or 23W CFL	Contains 366 Pieces of Tiffany Glass
TF878T	23" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 366 Pieces of Tiffany Glass
TF878UVB	70" H, 14" W, 14" Dp.	1-150W Med. Base or 40W CFL	Contains 366 Pieces of Tiffany Glass

Stephen COLLECTION

t I F F A N Y

FINISH:
Vintage Bronze



TFST2822VB 



TFST2840VB   

 **TFST5103VB**



 **TF885SVB**



Stephen COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFST2822VB*	27.5" H, 21.5" W, 21.5" Dp.	7"	4-100W Med. Base or 23W CFL	Contains 368 Pieces of Tiffany Glass
TFST2840VB**	43" H, 40" W, 40" Dp.	7.75"	8-100W Med. Base or 23W CFL	Contains 615 Pieces of Tiffany Glass
TFST5103VB*	19.5" H, 24" W, 24" Dp.	5.125"	3-100W Med. Base or 23W CFL	Each Shade Contains 152 Pieces of Tiffany Glass
TF885SVB	14.5" H, 14" W, 14" Dp.	6.5"	2-100W Med. Base or 23W CFL	Contains 248 Pieces of Tiffany Glass

*Chain-hung fixtures come with 8' of wire and 4' of chain. **Chain-hung fixture comes with 12' of wire and 8' of chain.

Stephen COLLECTION

FINISH:

Vintage Bronze

TFST8701VB



TF885F



TFST1508VB



TF1018TVB



Stephen COLLECTION


PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	
TF885F	59.5" H, 18" W, 18" Dp.	-	-	2-100W Med. Base or 23W CFL	Contains 256 Pieces of Tiffany Glass
TF885T	23" H, 16" W, 16" Dp.	-	-	2-75W Med. Base or 18W CFL	Contains 248 Pieces of Tiffany Glass
TF1018TVB	12" H, 5" W, 5" Dp.	-	-	1-25W Cand. Base	Contains 124 Pieces of Tiffany Glass
TFST1508VB	6" H*, 8" W, 8" Dp.	5.5"	-	1-100W Med. Base or 23W CFL	Contains 152 Pieces of Tiffany Glass
TFST8701VB	10" H, 8" W, 10.5" Dp.	5" x 5"	7.5"	1-100W Med. Base or 23W CFL	Contains 152 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

t I F F A N Y



From the **STEPHEN COLLECTION:**

 **TF885T**

Monteclair COLLECTION

FINISH: Western Bronze

GLASS: Tiffany & Mica

QUOIZEL
NATURALS
MICA

TFMC1818WT



Pull
CHAIN

TFMC2818WT




NEW!

FOR ♦ 2016

TFMC1508WT



TFMC1715WT



detail

Monteclair COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFMC1508WT	8" H*, 7.5" W, 7.5" Dp.	5"	1-60W Med. Base or 13W CFL	Contains 236 Pieces of Tiffany & Mica Glass
TFMC1715WT	13" H, 15" W, 15" Dp.	6"	2-60W Med. Base or 13W CFL	Contains 252 Pieces of Tiffany & Mica Glass
TFMC1818WT	10" H, 18" W, 18" Dp.	5"	3-60W Med. Base or 13W CFL	Contains 252 Pieces of Tiffany & Mica Glass
TFMC2818WT	22" H, 18" W, 18" Dp.	5"	3-60W Med. Base or 13W CFL	Contains 252 Pieces of Tiffany & Mica Glass

All chain-hung fixtures come with 8' of wire and 4' of chain. All rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" Rods.

BelleFleur COLLECTION

t I F F A N Y

FINISH:
Vintage Bronze

DAMP TFBF348VB



DAMP TFBF9362VB



DAMP TF1781VB

BelleFleur COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1781VB	28" H, 23" W, 23" Dp.	6"	4-100W Med. Base or 23W CFL	Contains 608 Pieces of Tiffany Glass
TFBF348VB	18" H, 48" W, 16" Dp.	8" x 4.5"	3-100W Med. Base or 23W CFL	Contains 884 Pieces of Tiffany Glass
TFBF9362VB	62" H, 20" W, 20" Dp.	-	3-100W Med. Base or 23W CFL	Contains 532 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.



From the **WEST END COLLECTION:**
TF1541VB

WestEnd COLLECTION

t I F F A N Y

FINISH:

VB Vintage Bronze **BB** Brushed Bullion

TF1541VB



TF9320BB



PULL CHAIN

TF6660BB



TF1400SVB

WestEnd COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1400SVB	6" H, 17" W, 17" Dp.	-	2-75W Med. Base or 18W CFL	Contains 262 Pieces of Tiffany Glass
TF1541VB	8.5" H*, 6" W, 6" Dp.	5"	1-100W Med. Base or 23W CFL	Contains 153 Pieces of Tiffany Glass
TF6660BB	26.5" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 306 Pieces of Tiffany Glass
TF9320BB	60" H, 18" W, 18" Dp.	-	2-100W Med. Base or 23W CFL	Contains 306 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. * Comes with (2) 6" and (2) 12" Rods.



TF1791TWT

*P*omeroy

FINISH: Western Bronze



TF9397VB



TF6668VB

*G*otham

FINISH: Vintage Bronze



PRODUCT	DIMENSIONS	BULBS	
TF1791TWT	21" H, 13" W, 15" Dp.	1-75W Med. Base or 18W CFL	Contains 4 Pieces of Tiffany Glass Panels
TF6668VB	24.5" H, 19" W, 19" Dp.	2-75W Med. Base or 18W CFL	Contains 48 Pieces of Tiffany Glass
TF9397VB	62" H, 20.5" W, 20.5" Dp.	2-100W Med. Base or 23W CFL	Contains 64 Pieces of Tiffany Glass


Hyacinth COLLECTION

t i F F A n Y

FINISH:
Vintage Bronze

DAMP TF1618VB

DAMP TF1737VB



DAMP TF1438VB

DAMP TF1536VB



The Hyacinth Tiffany glass design is one of our prettiest and most vibrant. Watch it add color and style to your home décor!

Hyacinth COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1438VB†	26.5" H, 22" W, 22" Dp.	5"	3-100W Med. Base or 23W CFL	Contains 540 Pieces of Tiffany Glass
TF1536VB	8.5" H*, 9" W, 9" Dp.	5.5"	1-100W Med. Base or 23W CFL	Contains 188 Pieces of Tiffany Glass
TF1618VB†	15" H, 22" W, 22" Dp.	6.25"	3-100W Med. Base or 23W CFL	Contains 540 Pieces of Tiffany Glass
TF1737VB††	11.5" H, 12.5" W, 12.5" Dp.	6.25"	1-150W Med. Base or 40W CFL	Contains 295 Pieces of Tiffany Glass

Rod-hung fixture comes with 10' of wire. *Comes with (2) 6" and (2) 12" Rods. †Chain-hung fixtures come with 8' of wire and 4' of chain.

††Fixture comes with 12' of wire and 8' of chain.

INTEGRATED LED
10 YEAR WARRANTY



TF1860FZ



TF7110ZLED

Pueblo
FINISH: Medici Bronze

TF9152ZLED



TF1860TZ

Montgomery
FINISH: Medici Bronze

LED CHART

TF7110ZLED / TF9152ZLED / TF1860TZ TF1860FZ	
Lumens	519
Total Watts	5W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3117K
Dimmable	No

PRODUCT	DIMENSIONS	LIGHT SOURCE	
TF1860FZ	51" H, 22.5" W, 9" Dp.	See LED Chart	Contains 40 Pieces of Tiffany Glass
TF1860TZ	19" H, 19" W, 6" Dp.	See LED Chart	Contains 40 Pieces of Tiffany Glass
TF7110ZLED	19" H, 19" W, 6" Dp.	See LED Chart	Contains 42 Pieces of Tiffany Glass
TF9152ZLED	51" H, 22.5" W, 9" Dp.	See LED Chart	Contains 42 Pieces of Tiffany Glass



From the **PUEBLO COLLECTION:**
TF7110ZLED



Jewel DRAGONFLY

FINISH: Malaga

TFJD2836ML

TFJD2822ML



Dragonfly Tiffanys are particularly intricate in their handcrafted artistry.




PRODUCT	DIMENSIONS	CANOPY	BULBS	
TFJD2822ML*	24" H, 22" W, 22" Dp.	5"	4-100W Med. Base or 23W CFL	Contains 315 Pieces of Tiffany Glass
TFJD2836ML**	36.5" H, 35.5" W, 35.5" Dp.	5"	6-100W Med. Base or 23W CFL	Contains 540 Pieces of Tiffany Glass

*Chain-hung fixture comes with 8' of wire and 4' of chain. **Chain-hung fixture comes with 12' of wire and 8' of chain.



 **TF1508FVB**

King
FINISH: Vintage Bronze



TF1508TVB 
Enlarged for detail



Copperfly
FINISH: Imperial Bronze

TF1851TIB 

PRODUCT	DIMENSIONS	BULBS	
TF1508FVB	62" H, 18" W, 18" Dp.	2-100W Med. Base or 23W CFL	Contains 318 Pieces of Tiffany Glass
TF1508TVB	24" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 318 Pieces of Tiffany Glass
TF1851TIB	16.5" H, 17" W, 17" Dp.	2-75W Med. Base or 18W CFL	Contains 324 Pieces of Tiffany Glass



Arden



TF1135T

Enlarged for detail

TF1135F



TF1672TWT



Revere

FINISH: Western Bronze

PRODUCT

DIMENSIONS

BULBS

TF1135F

59.5" H, 18" W, 18" Dp.

2-100W Med. Base or 23W CFL

Contains 192 Pieces of Tiffany Glass

TF1135T

23.5" H, 16" W, 16" Dp.

2-60W Med. Base or 13W CFL

Contains 192 Pieces of Tiffany Glass

TF1672TWT

22" H, 14" W, 14" Dp.

2-60W Med. Base or 13W CFL

Contains 196 Pieces of Tiffany Glass

Tiffany ANIMALS



TFX1520T

AngelFISH

Contains 39 Pieces of Tiffany Glass



TFX1519T

FlowerTURTLE

Contains 111 Pieces of Tiffany Glass



GreenFROG

TFX837Y

Contains 104 Pieces of Tiffany Glass



TF6031VB

Flowered LADYBUG

FINISH: Vintage Bronze

Contains 62 Pieces of Tiffany Glass



TFX1518T

RainbowBUTTERFLY

Contains 59 Pieces of Tiffany Glass



TF6033VB

LoungingFROG

FINISH: Vintage Bronze


Contains 55 Pieces of Tiffany Glass
and 4 jewels

TF6599R

OrangeBUTTERFLY

FINISH: Architectural Bronze

Contains 84 Pieces of Tiffany Glass



PRODUCT

DIMENSIONS

BULBS

TF6031VB

4" H, 7" W, 6" Dp.

1-15W T7 Cand. Base Supplied

TF6033VB

3.5" H, 8" W, 7" Dp.

1-15W T7 Cand. Base Supplied

TF6599R

9" H, 6" W, 7.5" Dp.

1-15W T7 Cand. Base Supplied

TFX1518T

9" H, 5" W, 5" Dp.

1-15W T7 Cand. Base Supplied

TFX1519T

3.5" H, 5.5" W, 8" Dp.

1-15W T7 Cand. Base Supplied

TFX1520T

6" H, 3" W, 2" Dp.

1-15W T7 Cand. Base Supplied

TFX837Y

6" H, 8.5" W, 9" Dp.

1-15W T7 Cand. Base Supplied



*P*urple WISTERIA

TF1139T 

 TF6034R



*L*aburnum
FINISH: Architectural Bronze



*L*ynch

TF1487T 

PRODUCT	DIMENSIONS	BULBS	
TF1139T	19.5" H, 10.5" W, 10.5" Dp.	1-60W Med. Base or 13W CFL	Contains 479 Pieces of Tiffany Glass
TF1487T	26" H, 15.5" W, 15.5" Dp.	2-75W Med. Base or 18W CFL	Contains 371 Pieces of Tiffany Glass
TF6034R	31" H, 22" W, 22" Dp.	3-100W Med. Base or 23W CFL	Contains 1998 Pieces of Tiffany Glass

Mariah

FINISH: Vintage Bronze



TFMH1820VB 

PULL CHAIN



 TF1575TIB

LED LIGHT

Berkshire

FINISH: Imperial Bronze



TF1850TIB 

Jewel

FINISH: Imperial Bronze

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1575TIB	27.5" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL +1-1W LED (Supplied)	Contains 363 Pieces of Tiffany Glass
TF1850TIB	23.5" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 297 Pieces of Tiffany Glass
TFMH1820VB	12" H, 20" W, 20" Dp.	7"	3-100W Med. Base or 23W CFL	Contains 336 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

Alahambre

FINISH: Vintage Bronze

TF1816VB



TF1408SVB DAMP



Reed

FINISH: Vintage Bronze

Graham

FINISH: Vintage Bronze



TF1409SVB DAMP

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1408SVB	6" H, 17" W, 17" Dp.	1" x 7"	2-75W Med. Base or 18W CFL	Contains 308 Pieces of Tiffany Glass
TF1409SVB	6" H, 17" W, 17" Dp.	1" x 7"	2-75W Med. Base or 18W CFL	Contains 186 Pieces of Tiffany Glass
TF1816VB	25" H, 22" W, 22" Dp.	5.5"	4-100W Med. Base or 23W CFL	Contains 128 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

Indus

FINISH: Vintage Bronze



TF6669VB

Grove Park

FINISH: Multi



TF9404M

GEOMETRIC
IRON ACCENTS



TF6898M

PRODUCT

TF6669VB

DIMENSIONS

23" H, 16" W, 16" Dp.

BULBS

2-60W Med. Base or 13W CFL

Contains 105 Pieces of Tiffany Glass

TF6898M

23.5" H, 14" W, 14" Dp.

2-60W Med. Base or 13W CFL

Contains 240 Pieces of Tiffany Glass

TF9404M

60" H, 17" W, 17" Dp.

2-100W Med. Base or 23W CFL

Contains 240 Pieces of Tiffany Glass



Lucia

TF1868T 



 TF1873T

QueensMeadow



 TF6826VB

Connie

FINISH: Vintage Bronze

PRODUCT

DIMENSIONS

BULBS

TF1868T

24.5" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL

Contains 690 Pieces of Tiffany Glass

TF1873T

23.5" H, 20" W, 20" Dp.

2-75W Med. Base or 18W CFL

Contains 498 Pieces of Tiffany Glass

TF6826VB

22" H, 14" W, 14" Dp

2-60W Med. Base or 13W CFL

Contains 387 Pieces of Tiffany Glass

DAMP TF1901VB



Adriana

FINISH: Vintage Bronze



detail



Florentine

FINISH: Vintage Bronze

50 DAMP TF1784VB

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF1784VB	39" H, 40" W, 40" Dp.	5.5"	8-100W Med. Base or 23W CFL	Contains 2331 Pieces of Tiffany Glass
TF1901VB	28" H, 32" W, 32" Dp.	5.5"	6-100W Med. Base or 23W CFL	Contains 515 Pieces of Tiffany Glass

All chain-hung fixtures come with 12' of wire and 8' of chain.

NEW!
FOR ♦ 2016




TF2076TVB

Enlarged for detail

Lance

FINISH: Vintage Bronze



TF2076FVB



TF1433T

Pearson

PRODUCT	DIMENSIONS	BULBS	
TF1433T	23" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 240 Pieces of Tiffany Glass
TF2076FVB	60" H, 20" W, 20" Dp.	2-100W Med. Base or 23W CFL	Contains 195 Pieces of Tiffany Glass
TF2076TVB	25" H, 19.5" W, 19.5" Dp.	2-75W Med. Base or 18W CFL	Contains 180 Pieces of Tiffany Glass



Ava

FINISH: Vintage Bronze

TFAV1714VB DAMP



TF489T

DAMP **TF489P01VB**



Chastain

PRODUCT	DIMENSIONS	CANOPY	BULBS	
TF489T	22.5" H, 15.5" W, 15.5" Dp.	-	2-60W Med. Base or 13W CFL	Contains 140 Pieces of Tiffany Glass
TF489P01VB	14" H*, 5" W, 5" Dp.	5.5"	1-100W Med. Base or 23W CFL	Contains 51 Pieces of Tiffany Glass
TFAV1714VB	9" H, 14" W, 14" Dp.	1.5' x 11"	2-60W Med. Base or 13W CFL	Contains 342 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. *Comes with (2) 6" and (2) 12" rods.



Bryant



TF1427T 

TF1427F 

 TF1021TVB

Holmes

FINISH: Vintage Bronze



PRODUCT	DIMENSIONS	BULBS	
TF1021TVB	12" H, 5" W, 5" Dp.	1-25W Cand. Base	Contains 84 Pieces of Tiffany Glass
TF1427F	60" H, 17" W, 17" Dp.	2-100W Med. Base or 23W CFL	Contains 112 Pieces of Tiffany Glass
TF1427T	23" H, 14" W, 14" Dp.	2-75W Med. Base or 18W CFL	Contains 112 Pieces of Tiffany Glass



TF1916TRS 

Bragg Creek

FINISH: Russet



TFNO6325VA 

Navajo

FINISH: Valiant Bronze



 **TF2095TRS**

NEW!

FOR ♦ 2016

Gibbons

FINISH: Russet

PRODUCT

TF1916TRS

TF2095TRS

TFNO6325VA

DIMENSIONS

24.5" H, 16" W, 16" Dp.

22.5" H, 14" W, 14" Dp.

25" H, 15" W, 15" Dp.

BULBS

2-75W Med. Base or 18 CFL

2-75W Med. Base or 18W CFL

2-75W Med. Base or 18W CFL

Contains 72 Pieces of Tiffany Glass

Contains 172 Pieces of Tiffany Glass

Contains 292 Pieces of Tiffany Glass

Palmetto


FINISH: Imperial Bronze



TF1848TIB

Fields

FINISH: Western Bronze



TF1425TWT



TFCB6325VB

Cambridge

FINISH: Vintage Bronze

PRODUCT

DIMENSIONS

BULBS

TF1425TWT

24" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL

Contains 330 Pieces of Tiffany Glass

TF1848TIB

26.5" H, 18" W, 18" Dp.

2-75W Med. Base or 18W CFL

Contains 186 Pieces of Tiffany Glass

TFCB6325VB

23.5" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL

Contains 318 Pieces of Tiffany Glass

Viking

FINISH: Vintage Bronze



TF1917TVA



India

FINISH: Imperial Bronze

TF1846TIB



TF1913TRS

Jewel Heart

FINISH: Russet

PRODUCT

TF1846TIB

TF1913TRS

TF1917TVA

DIMENSIONS

19.5" H, 16" W, 16" Dp.

23" H, 14" W, 14" Dp.

25.5" H, 16" W, 16" Dp.

BULBS

2-75W Med. Base or 18W CFL

2-60W Med. Base or 13W CFL

2-75W Med. Base or 18W CFL

Contains 282 Pieces of Tiffany Glass

Contains 224 Pieces of Tiffany Glass

Contains 260 Pieces of Tiffany Glass

TF1783CIB 



Lennon

FINISH: Imperial Bronze

Kelso

NEW!
FOR ♦ 2016



 TF2041T

TFCC8802



Classic Craftsman

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS	
TF1783CIB	17.5" H, 16" W, 16" Dp.	5"	-	4-60W Cand. Base	Contains 24 Pieces of Tiffany Glass
TF2041T	24" H, 15" W, 15" Dp.	-	-	2-75W Med. Base or 18W CFL	Contains 52 Pieces of Tiffany Glass
TFCC8802	7" H, 16.5" W, 5.5" Ext	-	2.5	2-60W Cand. Base	Contains 116 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.



From the **STOCKTON**
COLLECTION:
Q1056FPN (p. 514)

*Please see our Portables Catalog
(CQP3017X) for an exclusive presentation
of portable products and mirrors.*

Kingsley COLLECTION

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
SHADE: **BN** White Hardback Fabric with Double Trim
PN Cream Hardback Fabric Shade with Double Trim

NEW!
FOR ♦ 2016



VVKY9658BN



VVKY9258BN



VVKY9258PN

VVKY9658PN



VVKY9558BN



VVKY9558PN






VIVID provides **3 times the light output** of single socket lamps.

Our ViViD 3-Light Cluster features:

- Easy Turn Switch
- 3 Light levels
- Your choice:
Edison bulbs, Retro-Fit Fluorescent Bulbs, or Retro-Fit LED bulbs



VVKY9358BN



VVKY9358PN



VVKY6328PN

Enlarged for detail



VVKY6328BN

NEW!
FOR ♦ 2016

Kingsley COLLECTION

PRODUCT	DIMENSIONS	BULBS	SHADE
VVKY6328BN/PN	28" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL	(10" x 12") x (12" x 15") x 15"
VVKY9258BN/PN	58" H, 16" W, 16" Dp.	3-75W Med. Base or 18W CFL	(10" x 13") x (13" x 16") x 16"
VVKY9358BN/PN	61" H, 16" W, 16" Dp.	3-75W Med. Base or 18W CFL	(10" x 13") x (13" x 16") x 16"
VVKY9558BN/PN	58" H, 16" W, 16" Dp.	3-75W Med. Base or 18W CFL	(10" x 13") x (13" x 16") x 16"
VVKY9658BN/PN	58" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL + 3-75W Med. Base or 18W CFL	(10" x 13") x (13" x 16") x 16"

INTEGRATED LED
10 YEAR WARRANTY

VVBT6220WT

Enlarged for detail

VVBT9348WT

LED CHART

VVBT6220WT / VVBT9348WT

Lumens	507
Total Watts	5W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3053K
Dimmable	Yes

Benedict

FINISH: Western Bronze
GLASS: Frosted

NEW!
FOR ♦ 2016



VVCS9556OI

Cruise

FINISH: Oil Rubbed Bronze
SHADE: Cream Linen Hardback Fabric with Self Trim Top and Bottom

VVCS6332OI

VVCS9360OI

CLEAR GLASS ACCENT



PRODUCT	DIMENSIONS	BULBS/LIGHT SOURCE	SHADE DIMS.
VVBT6220WT	20" H, 17" W, 8" Dp.	See LED chart	-
VVBT9348WT	48" H, 20.5" W, 11" Dp.	See LED chart	-
VVCS6332OI	32.5" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL	10" x 12" x 15"
VVCS9360OI	58.5" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL	10" x 12" x 15"
VVCS9556OI	55.5" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL	10" x 12" x 15"

Ambrose

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
SHADE: Geneva White Hardback Fabric



VVAM9362BN

Enlarged for detail



VVAM6130PN

Enlarged for detail



VVAM6130BN



VVAM9362PN

QUOIZEL
NATURALS
MICA

Whitney

FINISH: imperial Bronze

INTEGRATED LED
 10 YEAR WARRANTY



VVWH9348IB



LED CHART

VVWH9348IB

Lumens	507
Total Watts	5W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3053K
Dimmable	Yes

PRODUCT	DIMENSIONS	BULBS/LIGHT SOURCE	SHADE DIMS.
VVAM6130BN/PN	30.5" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL	15" x 15" x 10"
VVAM9362BN/PN	62.5" H, 17" W, 17" Dp.	3-75W Med. Base or 18W CFL	15" x 15" x 10"
VVWH9348IB	49" H, 20.5" W, 11" Dp.	See LED chart	-



Spencer

FINISH: **BN** Brushed Nickel
WT Western Bronze



VVSP9348WT



VVSP9348BN

INTEGRATED LED
10 YEAR WARRANTY



VVTH9348AB



VVTH9348IB

Thompson

FINISH: **AB** Aged Brass
IB Imperial Bronze

LED CHART

VVTH9348AB/IB / VVSP9348BN/WT

Lumens	645
Total Watts	7W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3054K
Dimmable	Yes

PRODUCT

VVSP9348BN/WT

DIMENSIONS

47.5" H, 21" W, 11" Dp.

LIGHT SOURCE

See LED chart

VVTH9348AB/IB

49" H, 21" W, 11" Dp.

See LED chart

Buckler

FINISH: BN Brushed Nickel PN Palladian Bronze
SHADE: Off-White Hardback Fabric



Q1632TPN

Enlarged for detail

OPTIC
GLASS



Q1633FBN



Q1634TPN



Q1634TBN



Q1634FPN

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1632TPN	24" H, 12" W, 12" Dp.	1-100W Med. Base or 23W CFL	8" x 12" x 12"
Q1634TBN/TPN	29.5" H, 15" W, 15" Dp.	1-150W Med. Base or 40W CFL	11" x 13" x 15"
Q1633FBN	60" H, 15" W, 15" Dp.	1-100W Med. Base or 23W CFL	10" x 13" x 15"
Q1634FPN	60" H, 15" W, 15" Dp.	1-100W Med. Base or 23W CFL	10" x 13" x 15"

Stockton

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
SHADE: **BN** White Softback **PN** Cream Softback

 **Q1054FPN**



Q1054FBN 



Q1056FBN 



Q1056FPN 

 **Q1054TBN**

Enlarged for detail



 **Q1054TPN**



PRODUCT

DIMENSIONS

BULBS

SHADE DIMS.

Q1054FBN/FPN

60" H, 16" W, 16" Dp.

1-150W Med. Base or 40W CFL

11" x 9" x 16"

Q1054TBN/TPN

27" H, 15" W, 15" Dp.

1-100W Med. Base or 23W CFL

10.5" x 8" x 15"

Q1056FBN/FPN

61" H, 15" W, 15" Dp.

1-100W Med. Base or 23W CFL

11" x 7" x 15"



Q1055FBN 



Q1055FPN 

Stockton

FINISH: **BN** Brushed Nickel **PN** Palladian Bronze
SHADE: **BN** White Softback **PN** Cream Softback



 **Q1073FPN**



Q1072TPN 

 **Q1072FPN**



Archer

FINISH: Palladian Bronze
SHADE: Cream Softback Fabric



Q1074FPN

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1055FBN/FPN	60.5" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	11" x 9" x 16"
Q1072FPN	60.5" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	11" x 9" x 16"
Q1072TPN	26" H, 15" W, 15" Dp.	1-100W Med. Base or 23W CFL	10.5" x 8" x 15"
Q1073FPN	59.5" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	11" x 9" x 16"
Q1074FPN	61" H, 15" W, 15" Dp.	1-100W Med. Base or 23W CFL	11" x 7" x 15"

Humphrey

FINISH: **AB** Aged Brass
PN Palladian Bronze



Q1919TPN

Q1919TAB

Enlarged for detail

Q1918TPN

Enlarged for detail



Q1918TBN



Innovation

FINISH: **BN** Brushed Nickel
PN Palladian Bronze

INTEGRATED LED
10 YEAR WARRANTY

Jensen

FINISH: **AB** Aged Brass
BN Brushed Nickel

Q1852TAB



Q1852TBN

Enlarged for detail

LED CHART

	Q1852TAB/TBN	Q1918TBN/TPN	Q1919TAB/TPN
Lumens	507	360	360
Total Watts	5W	5W	5W
Color Rendering Index (CRI)	82	80	80
Color Temperature (CCT)	3053K	3000K	3000K
Dimmable	Yes	Yes	Yes



PRODUCT

Q1852TAB/TBN

DIMENSIONS

20.5" H, 21.5" W, 6.5" Dp.

LIGHT SOURCE

See LED chart

Q1918TBN/TPN

14" H, 5.5" W, 5.5" Dp.

See LED chart

Q1919TAB/TPN

14" H, 4.5" W, 4.5" Dp.

See LED chart



SUNSET BRASS ACCENTS

Q1889FOI

Haskell

FINISH: Oil Rubbed Bronze

Q1892FOI

Lyndhurst

FINISH: Oil Rubbed Bronze
SHADE: Tan Linen Hardback Fabric



H-H OFF SWITCH

Q1914T



Q1893FOI

OPTIC CRYSTAL

Jenkins

FINISH: Oil Rubbed Bronze
SHADE: Cream Linen Hardback



Weaving

SHADE: White Linen Hardback

Gray

SHADE: Grey Softback



Q1915T

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1889FOI	54.5" H, 18" W, 10" Dp.	1-60W Med. Base or 13W CFL	-
Q1892FOI	58.5" H, 14" W, 14" Dp.	1-150W Med. Base or 40W CFL	7.5" x 13" x 14"
Q1893FOI	56.5" H, 21" W, 14" Dp.	1-75W Med. Base or 18W CFL + 1-7W Cand. Base	7.5" x 12" x 14"
Q1914T	26" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	10" x 15" x 16"
Q1915T	27.5" H, 18" W, 12.5" Dp.	1-150W Med. Base or 40W CFL	(12" x 16") x (9" x 18") x 12.5"

Marx

FINISH: **BN** Brushed Nickel
WT Western Bronze



Q2125TWT

NEW!

FOR ♦ 2016

Q2125TBN

Enlarged for detail



Sway

FINISH: **T** Painted Blue Gray Combo
T1 Black Combo

Q2313T1

Q2313T

Enlarged for detail



Q2312T

Enlarged for detail

Q2312T1



LED CHART

	Q2312T/T1 / Q2313T/T1	Q2125TBN/WT
Lumens	300	450
Total Watts	3W	2.5W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	No	Yes

Encore

FINISH: **T** Black Combo
T1 Gray Combo

PRODUCT

Q2125TBN/TWT

DIMENSIONS

19" H, 15" W, 7.5" Dp.

LIGHT SOURCE

See LED chart

Q2312T/T1

18" H, 6" W, 2.5" Dp.

See LED chart

Q2313T/T1

16" H, 8" W, 7" Dp.

See LED chart



Westway

FINISH: **F** Painted Antique Gray
F1 Black Combo

Q2310F 

Enlarged for detail



Q2310F1 

NEW!

FOR ♦ 2016

Studio


FINISH: **T** Painted Gray
T1 Black Combo

Q2311T1

Enlarged for detail



Q2311T



Q2126FWT 

Enlarged for detail

Blaine

FINISH: Western Bronze

Q2126TWT 

PRODUCT	DIMENSIONS	BULBS
Q2126FWT	57" H, 18" W, 11" Dp.	1-100W Med. Base or 23W CFL
Q2126TWT	25" H, 13" W, 8" Dp.	1-100W Med. Base or 23W CFL
Q2310F/F1	49" H, 20" W, 11.5" Dp.	1-60W Med. Base or 13W CFL
Q2311T/T1	12" H, 7" W, 7" Dp.	1-60W Cand. Base



Q2314T 

Ocean

SHADE: White Fabric

Slade

FINISH: Western Bronze
SHADE: Cream Hardback



 **Q2127TWT**

NEW!

FOR ♦ 2016



Q2315T 

Blue River

SHADE: White Linen Fabric

 **Q2316T1**



 **Q2316T**

Dune

SHADE: **T** White Fabric
T1 Gold Fabric

PRODUCT

DIMENSIONS

BULBS

SHADE DIMS.

Q2127TWT

33" H, 16" W, 16" Dp.

1-150W Med. Base **or** 40W CFL

(11" x 14") x (14" x 16") x 16"

Q2314T

35" H, 17" W, 17" Dp.

2-60W Med. Base **or** 13W CFL

(10" x 15") x (15" x 17") x 17"

Q2315T

27.5" H, 16" W, 16" Dp.

1-150W Med. Base **or** 40W CFL

(10" x 14") x (14" x 16") x 16"

Q2316T/T1

22.5" H, 15" W, 15" Dp.

1-150W Med. Base **or** 40W CFL

(10" x 13") x (13" x 15") x 15"



Looping
SHADE: Gold Fabric

Q2320T 

Sable
SHADE: White Fabric



 Q2317T

NEW!
FOR ♦ 2016



Starling
SHADE: Gold Fabric

Q2319T 



Percy
SHADE: Gold Fabric

 Q2321T

Q2318T 

Aquatic
SHADE: White Fabric



PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q2317T	25.5" H, 14" W, 14" Dp.	1-100W Med. Base or 23W CFL	(9.5" x 12") x (12" x 14") x 14"
Q2318T	28.5" H, 15" W, 15" Dp.	2-60W Med. Base or 13W CFL	8" x 14.5" x 14.5"
Q2319T	30" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	(10" x 14") x (14" x 16") x 16"
Q2320T	29.5" H, 18" W, 18" Dp.	1-150W Med. Base or 40W CFL	10.5" x 18" x 18"
Q2321T	27" H, 17" W, 17" Dp.	1-150W Med. Base or 40W CFL	(11" x 15") x (15" x 17") x 17"



Barrel
SHADE: Gold Fabric

NEW!
FOR ♦ 2016

Q2322T



Q2324T

NEW!
FOR ♦ 2016

Seaside
SHADE: White Fabric



Q1630FPN

Abbey
FINISH: PalladianBronze
SHADE: Pleated Fabric

Sandy
SHADE: Gold Fabric

Q2323T

NEW!
FOR ♦ 2016



PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1630FPN	59" H, 15" W, 15" Dp.	1-100W Med. Base or 23W	10" x 11" x 15"
Q2322T	29" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	10" x 16" x 16"
Q2323T	30" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	(10" x 14") x (14" x 16") x 16"
Q2324T	29" H, 17" W, 17" Dp.	1-150W Med. Base or 40W CFL	(11" x 15") x (15" x 17") x 17"

Garnet

SHADE: White Linen Fabric




Q2325T 

NEW!

FOR  2016



SL702G 
SL701G



AB703A 


SatinLace

FINISH: French Gold Flemish



SL703G 



AB701A 
AB702A

Abigail Adams

FINISH: Antique Brass

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
AB701A	20" H, 8.5" W, 8.5" Dp.	1-75W Med. Base or 18W CFL + 1-7W C7 Cand. Base*	-
AB702A	24" H, 11" W, 11" Dp.	1-150W Med. Base or 40W CFL + 1-7W C7 Cand. Base*	-
AB703A	28" H, 14" W, 14" Dp.	1-150W Med. Base or 40W CFL + 1-7W C7 Cand. Base*	-
Q2325T	30" H, 16" W, 16" Dp.	1-150W Med. Base or 40W CFL	(10" x 14") x (14" x 16") x 16"
SL701G	20" H, 8" W, 8" Dp.	1-75W Med. Base or 18W CFL + 1-7W C7 Cand. Base*	-
SL702G	24" H, 10" W, 10" Dp.	1-150W Med. Base or 40W CFL + 1-7W C7 Cand. Base*	-
SL703G	28" H, 12.5" W, 12.5" Dp.	1-150W Med. Base or 40W CFL + 1-7W C7 Cand. Base*	-



Q1295KPK

Linear

FINISH: Polished Nickel

INTEGRATED LED
10 YEAR WARRANTY



Q4571A

Beckett

SHADE: Beige Linen Drum

LED CHART

	Q1295KPK
Lumens	507
Total Watts	5W
Color Rendering Index (CRI)	82
Color Temperature (CCT)	3053K
Dimmable	YES



QJF15078BTR



QJ6781TR

Glenhaven

FINISH: Teco Rossa

GLASS: Amber Etched



QM6904M

String Shade

FINISH: Combo

SHADE: Natural String

PRODUCT	DIMENSIONS	BULBS	SHADE DIMS.
Q1295KPK	28" H, 27.5" W, 27.5" Dp.	See LED chart	-
Q4571A	72.5" H, 53" W, 16" Dp.	1-150W Med. Base or 40W CFL	16" x 17"
QJ6781TR	18" H, 14" W, 14" Dp.	2-60W Med. Base or 13W CFL	-
QJF15078BTR	60.5" H, 18" W, 18" Dp.	2-75W Med. Base or 18W CFL	-
QM6904M	29" H, 19" W, 19" Dp.	1-150W Med. Base or 40W CFL	5" x 19" x 12"

Table & Floor

Please see referenced page numbers for larger images and full descriptions of these products.

Kyle
KY6328IB
 See page 73



Union Station
UST6127WT
 See page 140



CAROLYN KINDER
Confetti
CKCF6330OS
 See page 208



CAROLYN KINDER
Brookmont
CKBT1863T
 See page 212



CAROLYN KINDER
Hickman
CKHM1879T
 See page 212



Laguna
MC842TRC
 See page 229




Laguna
MC842FRC
 See page 229



Laguna
Q4574A
 See page 232



Alistar
MCAL9470IB
 See page 233



Alistar
MC1862IB
 See page 233



Prism
MC2042T
 See page 233



Cyrus
MCCS9357AS
 See page 234



Cyrus
MCCS9470AS
 See page 234



Cyrus
MCCS6326AS
 See page 234



San Gabriel
NX615TVA
 See page 234



Pearce
PER6323TB
 See page 236



Table & Floor

Please see referenced page numbers for larger images and full descriptions of these products.

Vega

MC1691TIB
See page 236



Highland

MC120T
See page 237



Tartan

MC2134TWT
See page 238



Whispering Wood

AG711TVA
See page 238



Pomez

TF135TBC
See page 243



Pomez

TF6825CN
See page 243



Pomez

TF135FBC
See page 243



Captiva

SSCV6222VB
See page 244



Captiva

SSCV6224VB
See page 244



Floret

SSFT6221VB
See page 244



Sanibel

SSSB6223VB
See page 245



Jade

JD2077TVB
See page 245



Please see the **Quoizel Tiffany Collection** on page 459 for many attractive art glass table and floor lamp solutions.

BRECKENRIDGE MIRROR
QR1419BN (p. 533)




*Please see our Portables Catalog
(CQP3017X) for an exclusive presentation
of portable products and mirrors.*



MIRRORS

QUOIZEL

Woodmere



NEW!
FOR ♦ 2016

QR1416



QR2060

Carrigan

GLASS: Beveled Frame and Mirror

Hearst

FINISH: **2053** Gold Leaf
2054 silver Leaf

QR2053



QR2057



NEW!
FOR ♦ 2016

NEW!
FOR ♦ 2016

QR2054



QR2058

Vanderbilt

FINISH: **2058** Palladian Bronze
2057 Century silver Leaf



PRODUCT

QR1416

QR2053/2054

DIMENSIONS

32" H, 26" W, 2" Dp.

30.5" H, 20.5" W, 3" Dp.

PRODUCT

QR2060

QR2057/2058

DIMENSIONS

39.5" H, 24" W, 1" Dp.

36" H, 24" W, 1" Dp.

NEW!
FOR ♦ 2016



QR2059

Finn

FINISH: Palladian Bronze

QR1253



Sage


Tallon

FINISH: **2055** ivory with Gold Highlights
2056 Century silver Leaf

NEW!
FOR ♦ 2016



QR2055



QR2056



QR42420BN

Soho

FINISH: Brushed Nickel

PRODUCT	DIMENSIONS
QR1253	30" H, 24" W, 1" Dp.
QR2055/2056	36" H, 36" W, 2" Dp.

PRODUCT	DIMENSIONS
QR2059	42" H, 42" W, 1" Dp.
QR42420BN	24" H, 20" W, 1.5" Dp.

Duchess

FINISH: Palladian Bronze
GLASS: Beveled

See p. 347 for matching
Duchess products.



DH44030PN

DH43024PN

Greystone

GLASS: Frameless, Beveled

QR1815

See setting shot for
QR1815 on page 341.



Jasper

FINISH: Brushed Nickel
GLASS: Beveled

JA43225BN

TY43625AN

Taylor


FINISH: Antique Nickel
GLASS: Beveled



See p. 367 for matching Taylor products.
See setting shot for TY43625AN on page 366.

PRODUCT	DIMENSIONS
DH43024PN	30" H, 24" W, 1.5" Dp.
DH44030PN	40" H, 30" W, 1.5" Dp.
JA43225BN	32" H, 24.5" W, 2" Dp.

PRODUCT	DIMENSIONS
QR1815	28" H, 22" W, 1" Dp.
TY43625AN	35.5" H, 25.5" W, 2" Dp.



QR983

Gwyneth
GLASS: Beveled



MY430241ML

QUOIZEL
NATURALS
PEN SHELL



MY430242ML



QR1922WT

Monterey Mosaic
FINISH: Malaga

See pages 81-86 for matching Monterey Mosaic products.
See setting shot for MY430241ML on pages 82-83.

Maxim
FINISH: Western Bronze

QR1864C

Shelburne
FINISH: Polished Chrome



PRODUCT	DIMENSIONS
MY430241ML	30" H, 24" W, 1.5" Dp.
MY430242ML	30" H, 24" W, 1.5" Dp.
QR983	39.5" H, 39.5" W, 2" Dp.

PRODUCT	DIMENSIONS
QR1922WT	37.5" H, 25" W, 1" Dp.
QR1864C	33" H, 25.5" W, 1" Dp.



Downtown

FINISH: Brushed Nickel

See p. 46-51 for matching Downtown products.

DW43222BN

QR1221C



Norton

FINISH: Polished Chrome



Ritz

FINISH: Polished Chrome
GLASS: Beveled

UPRZ43426C

Envision

GLASS: Frameless, Beveled

QR1814



UPRZ53426C



PRODUCT

DIMENSIONS

DW43222BN

32" H, 22" W, 1.5" Dp.

QR1221C

32" H, 22" W, 1.5" Dp.

QR1814

28" H, 22" W, 1" Dp.

PRODUCT

DIMENSIONS

UPRZ43426C

34" H, 26" W, 2" Dp.

UPRZ53426C

34" H, 26" W, 2" Dp.



QR1419PN



QR1419BN

Breckenridge

FINISH: **BN** Brushed Nickel
PN Palladian Bronze
GLASS: Beveled

Marcos

FINISH: Brushed Nickel



QR1857BN



QR1912WT

Vista

FINISH: Western Bronze

Ultra

GLASS: Beveled Frame and Mirror



NEW!

FOR ♦ 2016

Confetti

FINISH: Old silver

See pages 208-209 for matching Confetti products.



CKCF43624OS

Carolyne Kinder
INTERNATIONAL

CKUT1921

PRODUCT	DIMENSIONS
CKCF43624OS	35" H, 24" W, 1" Dp.
CKUT1921	36" H, 24" W, 2" Dp.
QR1419BN/PN	35" H, 21" W, 1" Dp.

PRODUCT	DIMENSIONS
QR1857BN	32" H, 24" W, 1" Dp.
QR1912WT	30" H, 30" W, 1" Dp.

MINI PENDANT RODS




Darkest Bronze



Imperial Bronze



Iron Gate



Mystic Black (matte)



Mottled Black



Mottled Silver



Vintage Gold

9006EX

6" H, .5" W, .5" Dp.

9012EX

12" H, .5" W, .5" Dp.

9006EXAN	9012EXAN	Antique Nickel
9006EXBA	9012EXBA	Royal Ebony
9006EXBN	9012EXBN	Brushed Nickel
9006EXC	9012EXC	Polished Chrome
9006EXCC	9012EXCC	Copper Canyon
9006D	9012EXD	Dusk Bronze
9006EXDC	9012EXDC	Dark Cherry
9006EXDK	9012EXDK	Darkest Bronze
9006EXES	9012EXES	Empire Silver
9006EXIB	9012EXIB	Imperial Bronze
9006EXIF	9012EXIF	Italian Fresco
9006EXIN01	9012EXIN01	Iron Gate
9006EXIS	9012EXIS	Imperial Silver
9006EXK	9012EXK	Mystic Black (matte)
9006EXK01	9012EXK01	Mystic Black (glossy)
9006EXLN	9012EXLN	Leathered Bronze
9006EXMB	9012EXMB	Mottled Black
9006EXMC	9012EXMC	Mottled Cocoa
9006EXML	9012EXML	Malaga
9006EXMM	9012EXMM	Mottled Silver
9006EXMN	9012EXMN	Millenia
9006EXOS	9012EXOS	Old Silver
9006EXOZ1	9012EXOZ1	Old Bronze
9006EXPN	9012EXPN	Palladian Bronze
9006EXRC	9012EXRC	Renaissance Copper
9006EXRK	9012EXRK	Rustic Black
9006EXRS	9012EXRS	Russet
	9012EXTB	Terra Bronze
9006EXTM	9012EXTM	Teco Marrone
9006EXVA	9012EXVA	Valiant Bronze
9006EXVB	9012EXVB	Vintage Bronze
9006EXVG	9012EXVG	Vintage Gold
9006EXWT	9012EXWT	Western Bronze
9016EXPN (16" L)		Palladian Bronze

9007EX, 9106EX

6" H, 1" W, 1" Dp.

9008EX, 9112EX

12" H, 1" W, 1" Dp.

9007EXAN	9008EXAN	Antique Nickel
9007EXBN01	9008EXBN01	Brushed Nickel
9007EXC	9008EXC	Polished Chrome
9007EXCC	9008EXCC	Copper Canyon
9007EXIS	9008EXIS	Imperial Silver
9007EXMM	9008EXMM	Mottled Silver
9007EXOS	9008EXOS	Old Silver
9007EXPN	9008EXPN	Palladian Bronze
9007EXRK	9008EXRK	Rustic Black
9007EXVA	9008EXVA	Valiant Bronze
9007EXWT	9008EXWT	Western Bronze
9106EXBN	9112EXBN	Brushed Nickel



Antique Nickel



Brushed Nickel



Imperial Silver



Palladian Bronze



Western Bronze

Finish Sample Guide

Quoizel lamps, lighting fixtures and mirrors are created in a variety of decorative finishes. Finish samples are available upon request. Please contact your sales representative for details.



OUTDOOR LIGHTING



PM9300IB

PM9300Z
Enlarged for detail



Pier Mounts

PM9300K



For Ground Mounting:
Please order post
(PO9110 followed by a
finish code).

For Column Mounting:
Please order pier mount
(PM9300 followed by a
finish code).

Please note:
The post does not fit
into the pier mount.

Post Mounts

PO9110IB



PO9110Z



PRODUCT

PM9300IB/K/Z

DIMENSIONS

3.5" H, 6" W, 6" Dp.

FINISH

IB = Imperial Bronze K = Mystic Black Z = Medici Bronze

PO9110IB/Z

84" H, 3" W, 3" Dp.

IB = Imperial Bronze Z = Medici Bronze



PO9120IB



PO9120K



PO9120Z




Round post detail

Post Mounts

P09120 – Round Post

P09130 – Fluted Post



Fluted post detail



PO9130IB



PO9130K



PO9130Z



PO9140K



PO9140Z

Post & skirt

PO9140IB

Enlarged for detail



PRODUCT

PO9120IB/K/Z

DIMENSIONS

84" H, 3" W, 3" Dp.

FINISH

IB = Imperial Bronze K = Mystic Black Z = Medici Bronze

PO9130IB/K/Z

84" H, 3" W, 3" Dp.

IB = Imperial Bronze K = Mystic Black Z = Medici Bronze

PO9140IB/K/Z

81" H, 10" W, 10" Dp.

IB = Imperial Bronze K = Mystic Black Z = Medici Bronze

A

AB701A	523
AB702A	523
AB703A	523
ABN5006RK	143, 144, 251
ABN5012RK	144, 251
ABN5024RK	142, 251
ADA2820LN	103, 273
ADA5006LN	103
ADA5009LN	102
ADA8702LN	103, 319
ADS1504DC	39, 284
ADS1615DC	39, 308
ADS2818DC	39, 272
ADS5005DC	38
ADS639DC	39, 255
ADS8701DC	38, 319
AG711TVA	238, 526
A11720IB	240, 301
A12824IB	240, 277
ALT8405WT	380
ALT8407WT	380
AME5005IB	109, 249
AME5009IB	109, 249
AME5018IB	108, 249
AME8701IB	109, 249, 319
AML2821OZ	265
AML5005OZ	162
AN8539ES	342
AN8540ES	342
AN8541ES	342
ANR5006IB	171, 252
ANR5010IB	171, 252
AS1716PN	241, 301
AS2818PN	241, 277
AS2824PN	241, 277
AX2820PN	104, 273
AX2826PN	104, 273
AX434PN	104, 254

B

BAN1911K	450
BAN8407K	450
BAN8409K	450
BAN8411K	448, 449
BAN9011K	450
BCN1716WT	45, 298
BCN2820WT	45, 272
BCN5006WT	45
BCN5009WT	44
BCN5204WT	45
BDR2820IB	238, 277
BDR5006IB	160, 251
BFD1910K	395
BFD1910PN	395
BFD8407K	395
BFD8407PN	395
BFD8408K	395

BFD8408PN	395
BFD8410K	394
BFD8410PN	395
BFD9010K	395
BFD9010PN	395
BGS1715RK	288
BGS5203RK	170
BGT8602BN	343
BGT8603BN	343
BGT8604BN	343
BHN5006VG	157, 251
BHN5009VG	157, 251
BHN5303VG	157, 251
BKH1714WT	42, 298
BKH5204WT	43
BKH5208WT	43
BKH5303WT	43
BKH838WT	42, 254
BKR1910K	405
BKR8406K	405
BKR8408K	371, 405
BKR8410K	404
BKR9010K	405
BND1613BA	307
BND1818BA	268
BNS1505WT	40, 284
BNS1715WT	41, 298
BNS2818WT	41, 272
BNS5005WT	41
BNS5009WT	40
BNS5204WT	41
BRN1910IB	435
BRN8406IB	435
BRN8408IB	435
BRN8410IB	435
BRN8412IB	434
BRN9010IB	435
BR01715MK	110, 250, 299
BR05203MK	110, 250
BR05204MK	110, 249
BRX1611C	176, 308
BRX1614C	175, 308
BRX1619C	175, 308
BRX1620C	176, 309
BRX1626C	176, 309
BRX2818C	174, 274
BRXA1614C	175, 308
BRXA1619C	175, 308
BWL1508CC	280
BWL1717CC	288
BWL2816CC	267
BWL2822CC	267
BWR8602BN	346
BWR8603BN	346
BWR8604BN	346

C

CAT1911PN	389
-----------	-----

CAT8407PN	389
CAT8409PN	389
CAT8411PN	388
CAT9011PN	389
CATL1911PN	387
CATL8407PN	387
CATL8409PN	387
CATL8411PN	386
CATL9011PN	387
CCR8406CU	441
CCR8408CU	441
CCR8410CU	441
CCR9010CU	441
CDY1508BN	280
CDY1714BN	297
CDY2814BN	270
CHB1612DK	106, 249, 308
CHB5204DK	106, 107, 249
CHB5206DK	106, 249
CHB5208DK	106, 249
CHI1911IB	457
CHI8407IB	457
CHI8409IB	457
CHI8411IB	457
CHI8413IB	456
CHI9011IB	457
CKBT1863T	212, 525
CKCF1508OS	209, 285
CKCF1508RK	209, 285
CKCF1714OS	209, 300
CKCF1717OS	209, 300
CKCF1717RK	209, 300
CKCF1720OS	209, 300
CKCF2816OS	209, 275
CKCF2816RK	209, 275
CKCF2822OS	207, 209, 275
CKCF2822RK	208, 275
CKCF2825OS	208, 275
CKCF2825RK	209, 275
CKCF339OS	209, 258
CKCF339RK	208, 258
CKCF43624OS	208, 533
CKCF6330OS	208, 525
CKGN1509MZ	215, 286
CKHM1879T	212, 525
CKKD1509WT	214, 215, 286
CKMO1716BN	210, 300
CKMO2820BN	210, 275
CKM05003BN	210, 211
CKMS1716TM	213, 300
CKMS2822TM	213, 276
CKMS442TM	213, 257, 258
CKNK1509BV	215, 286
CKSC5201DR	212
CKSN1507AR	215, 286
CKUT1921	212, 533
CLT1714BN	289
CLT5004BN	162
CM1912AC	422

CM8408AC	422
CM8410AC	423
CM8412AC	422
CM9012AC	422
COE8305WT	381
COE8405WT	381
COR1611CU	425
COR1611K	425
COR8409K	425
COR8410K	425
COR8412K	424
COR9010K	425
CP2820IB	268
CP5006IB	160
CRA1717MC	290
CRA2822MC	271
CRA2826MC	271
CRE5004FR	151
CS1718RK	111, 250, 299
CS5006RK	111, 250
CS5012RK	111, 250
CTH5003AN	147
CTH5006AN	147
CTH5009AN	146
CTH5204AN	147
CTO5204WT	168
CVW8406WT	401
CVW8407WT	401
CVW8408WT	401

D

DBN1506BN	282
DBN8602BN	345
DBN8603BN	344, 345
DBN8604BN	345
DE1490IB	429
DE8958IB	429
DE8959IB	429
DE8960IB	429
DE8961IB	428
DE8976IB	429
DE9256IB	429
DH1404AN	56, 312
DH1404PN	57, 311, 312
DH1506AN	57, 284
DH1506PN	56, 284
DH1718AN	57, 298
DH1718PN	56, 298
DH2820AN	54, 272
DH2820PN	54, 55, 272
DH348AN	54, 259
DH348PN	54, 259
DH43024PN	57, 530
DH44030PN	57, 530
DH5005AN	53
DH5005PN	53
DH5009AN	52
DH5009PN	53

KDN1510BN	252, 280
KDN5004BN	169, 252
KLT8602CLED	340
KLT8603CLED	340, 341
KLT8604CLED	340
KPR5005BN	162
KY1404IB	72, 247, 312, 314
KY1507IB	69, 73, 247, 284
KY1507IN	73, 247, 284
KY1508IB	73, 247, 284
KY1508IN	73, 247, 284
KY1716IB	72, 247, 298
KY2822IB	69, 72, 247, 272
KY433IB	71, 247, 260
KY5006IB	71, 247
KY5006IN	70, 247
KY5009IB	71, 247
KY5009IN	70, 247
KY5016IB	68, 247
KY5103IB	71, 247
KY5103IN	71, 247
KY5106IB	70, 247
KY540IB	71, 247, 260
KY540IN	71, 247, 260
KY5503IB	72, 247
KY5506IB	72, 247
KY6328IB	73, 227, 247, 525
KY8701IB	73, 247, 319
KY8701IN	73, 247, 319
KY8801IB	73, 247, 319
KY8801IN	73, 247, 319

L

LBH2820WT	271
LDG1909K	417
LDG8406K	417
LDG8408K	417
LDG8409K	416
LDG9009K	417
LFT8602C	355
LFT8603C	355
LFT8604C	355
LKE5204VG	141, 168
LLA1615RA	116, 308
LLA5203RA	116
LLA5204RA	116
LLA5205RA	116
LP1505IB	76, 284
LP5006IB	75
LP5009IB	75
LP5018IB	74
LP639IB	76, 259
LP8601IB	76, 319
LSM8801GY	318
LSM8801PS	318
LSM8801TM	318

M

MBH1911K	400
MBH1911PN	400
MBH8407K	400
MBH8407PN	399, 400
MBH8409K	400
MBH8409PN	400
MBH8411K	398
MBH8411PN	398
MBH9011K	400
MBH9011PN	400
MBK1716VG	113, 299
MBK2820VG	113, 273
MBK5005VG	112, 113
MC120T	237, 526
MC1691TIB	236, 526
MC1862TIB	233, 525
MC1910MM	235, 277
MC2042T	233, 525
MC2134TWT	238, 526
MC8420CRC	228, 276, 277
MC842CRC	228, 231, 277
MC842FRC	229, 525
MC842PRC	230, 232, 286
MC842SRC	228, 301
MC842TRC	229, 525
MCAL9470IB	233, 525
MCBF1717WT	237, 301
MCBF2822WT	237, 277
MCCS6326AS	234, 525
MCCS9357AS	234, 525
MCCS9470AS	234, 525
MCKD1505TM	235, 286, 301
MCKD1715TM	235, 301
MCKD2819TM	235, 277
MCLG1612RC	229, 310
MCLG1616RC	229, 310
MCLG337RC	232, 254
MHE1910K	419
MHE1910VN	419
MHE8406K	419
MHE8406VN	419
MHE8409K	419
MHE8409VN	419
MHE8410K	419
MHE8410VN	418
MHE9010K	419
MHE9010VN	419
MIR1715VG	296
MIR1718VG	296
MIR2818VG	269
MJT5004BN	165
MJT5006BN	165
MJT5008BN	164
MJY1615VG	296
MJY5304VG	159
ML182AUL	302
ML182ESUL	302

ML182PNUL	302
ML182WUL	302
ML183A	302
ML183ES	302
ML183PN	302
ML183W	302
ML184A	302
ML184ES	302
ML184PN	302
ML184W	302
MLD8602BN	356
MLD8603BN	356
MLD8604BN	356
MLN8307K	458
MLN8309K	458
MLS1907IB	403
MLS8405IB	403
MLS8406IB	403
MLS8407IB	402
MLS9007IB	403
MMR5303C	159
MNO5006WT	167
MNO8602IS	357
MNO8603IS	357
MNO8604IS	357
MNR1611BN	303
MNR1611PN	303
MNR1613BN	303
MNR1613PN	303
MNR1615BN	303
MNR1615PN	303
MNT8404WT	372
MNT8405WT	372
MQ5003HL	77, 80
MQ5006HL	79
MQ5009HL	79
MQ5020HL	78
MQ5206HL	80
MQ5208HL	80
MQ8701HL	79, 319
MRE1506WT	281, 427
MRE1909WT	427
MRE8406WT	427
MRE8408WT	427
MRE8409WT	427
MRE8410WT	426
MRE9009WT	427
MRN5005IB	145
MRN5006IB	145
MRN5008IB	145
MTP1510AN	117, 285
MTP1718AN	117, 299
MTP2820AN	117, 273
MTP2823AN	117, 273
MTP5203AN	117
MY1404ML	85, 248, 312
MY1506ML	86, 248, 284
MY1613ML	85, 248, 308
MY1618ML	85, 248, 308

MY1718ML	85, 248, 298
MY1723ML	85, 248, 298
MY2816ML	84, 248, 273
MY2824ML	84, 248, 273
MY430241ML	82, 86, 248, 531
MY430242ML	86, 248, 531
MY5005ML	81, 248
MY5103ML	83, 84, 248
MY8801ML	83, 86, 248, 319

N

NA1510BN	119, 285
NA1514BN	119, 285
NA5103BN	118
NA8409PN	119, 458
NA8414PN	119, 458
NBE5005RK	129
NBE5008RK	129
NBE5009RK	128
NBE5303RK	129
NBE8702RK	129, 320
NGT8602BN	361
NGT8603BN	361
NGT8604BN	361
NHR1718WT	133, 299
NHR5204WT	133
NHR538WT	133, 256
NL8601BN	360
NL8601C	360
NL8601HO	360
NL8602BN	360
NL8602C	360
NL8602HO	360
NL8603BN	360
NL8603C	360
NL8603HO	360
NL8604BN	360
NL8604C	360
NL8604HO	360
NN8602BNLED	339
NN8603BNLED	339
NN8604BNLED	339
NX615TV	234, 525
NY1178A	378
NY1178AC	377
NY1178B	377
NY1178K	377
NY1178P	377
NY1178Z	377
NY1179A	377
NY1179AC	379
NY1179B	377
NY1179K	377
NY1179P	377
NY1179Z	377
NY1180A	377
NY1180AC	379
NY1180B	377

SLT5303IF.....	156	TB8603C.....	365	TF1868T.....	498	TFIK1404VA.....	315, 465
SMT1612BN.....	304	TB8604C.....	365	TF1873T.....	498	TFIK1508VA.....	465
SMT1612PN.....	304	TCA5004VP.....	137	TF1901VB.....	499	TFIK1509VA.....	468
SMT1614BN.....	304	TCA5006VP.....	137	TF1913TRS.....	505	TFIK1617VA.....	468
SMT1614PN.....	304	TCA5009VP.....	136	TF1916TRS.....	503	TFIK1714VA.....	465
SMT1617BN.....	304	TCA8701VP.....	137, 320	TF1917TVA.....	505	TFIK1817VA.....	464
SMT1617PN.....	304	TDR1909K.....	397	TF2041T.....	506	TFIK2817VA.....	464, 467
SNN1612K.....	385	TDR1909PN.....	397	TF2076FVB.....	500	TFIK348VA.....	262, 464
SNN1612PN.....	385	TDR8406K.....	397	TF2076TVB.....	500	TFIK6111VA.....	468
SNN1612W.....	385	TDR8406PN.....	397	TF2095TRS.....	503	TFIK8802.....	320, 468
SNN1909K.....	385	TDR8408K.....	397	TF489P01VB.....	501	TFIK9471VA.....	466
SNN1909PN.....	385	TDR8408PN.....	397	TF489T.....	501	TFJD2822ML.....	490
SNN1909W.....	385	TDR8409K.....	397	TF6031VB.....	493	TFJD2836ML.....	490
SNN8406K.....	385	TDR8409PN.....	396	TF6033VB.....	493	TFKM1508VB.....	477
SNN8406PN.....	385	TDR9009K.....	397	TF6034R.....	494	TFKM2840VB.....	477
SNN8406W.....	385	TDR9009PN.....	397	TF6599R.....	493	TFKM5103VB.....	476
SNN8408K.....	385	TF1018TVB.....	480	TF6660BB.....	485	TFMC1508WT.....	482
SNN8408PN.....	385	TF1021TVB.....	502	TF6668VB.....	486	TFMC1715WT.....	482
SNN8408W.....	385	TF1135F.....	492	TF6669VB.....	497	TFMC1818WT.....	482
SNN8409K.....	385	TF1135T.....	492	TF6825CN.....	243, 526	TFMC2818WT.....	482
SNN8409PN.....	385	TF1139T.....	494	TF6826VB.....	498	TFMH1820VB.....	495
SNN8409W.....	384	TF1180TVA.....	472, 473	TF6898M.....	497	TFNO6325VA.....	503
SNN9009K.....	385	TF135FBC.....	243, 526	TF7110ZLED.....	488, 489	TFST1508VB.....	480
SNN9009PN.....	385	TF135TBC.....	243, 526	TF878CVB.....	477	TFST2822VB.....	479
SNN9009W.....	385	TF1396SVB.....	478	TF878F.....	478	TFST2840VB.....	479
SNNL1909K.....	383	TF1400SVB.....	485	TF878T.....	478	TFST5103VB.....	479
SNNL1909PN.....	383	TF1408SVB.....	496	TF878UVB.....	478	TFST8701VB.....	320, 480
SNNL8406K.....	383	TF1409SVB.....	496	TF879F.....	475	TFT16191A1VA.....	466
SNNL8406PN.....	383	TF1425TWT.....	504	TF879T.....	475	TFVY1404VA.....	315, 460
SNNL8408K.....	383	TF1427F.....	502	TF885F.....	480	TFVY1716VA.....	460
SNNL8408PN.....	383	TF1427T.....	502	TF885SVB.....	479	TFVY2819VA.....	460
SNNL8409K.....	382	TF1433T.....	500	TF885T.....	481	TFVY6118VA.....	461
SNNL8409PN.....	383	TF1438VB.....	459, 487	TF9152ZLED.....	488	TFVY6325VA.....	461
SNNL9009K.....	383	TF1487T.....	494	TF9320BB.....	485	TFVY9359VA.....	461
SNNL9009PN.....	383	TF1507VB.....	242, 243, 286	TF9397VB.....	486	TFX1518T.....	493
SPH1508BN.....	132, 285	TF1508TVB.....	491	TF9404M.....	497	TFX1519T.....	493
SPH1508PN.....	132, 285	TF1508FVB.....	491	TFAS1404VA.....	315, 472	TFX1520T.....	493
SPH5005BN.....	132	TF1508VB.....	469	TFAS1507VA.....	471	TFX837Y.....	493
SPH5005PN.....	132	TF1536VB.....	278, 487	TFAS1615VA.....	470	THL1718MK.....	167
SPH5009BN.....	130	TF1541VB.....	484, 485	TFAS1714VA.....	472	THL5006MK.....	167
SPH5009PN.....	130, 131	TF1575TIB.....	495	TFAS1817VA.....	474	TML1908K.....	443
SPR8601C.....	363	TF1618VB.....	487	TFAS2817VA.....	471	TML8405K.....	443
SPR8602C.....	363	TF1672TWT.....	492	TFAS344VA.....	262, 471	TML8407K.....	443
SPR8603C.....	363	TF1714VB.....	469	TFAS5003VA.....	470	TML8408K.....	442
SPR8604C.....	363	TF1737VB.....	487	TFAS9360VA.....	474	TML9008K.....	443
SRA5204VG.....	169	TF1781VB.....	483	TFAS9470VA.....	474	TRG1508OZ.....	94, 284
SSCV6222VB.....	244, 526	TF1783CIB.....	506	TFAT1507VA.....	462	TRG1712OZ.....	95, 299
SSCV6224VB.....	244, 526	TF1784VB.....	499	TFAT1716VA.....	462	TRG1716OZ.....	95, 299
SSFT6221VB.....	244, 526	TF1791TWT.....	486	TFAT2821VA.....	462	TRG1816OZ.....	94, 273
SSSB1714VB.....	245, 301	TF1805SVB.....	469	TFAT6325VA.....	463	TRG5103OZ.....	92, 94
SSSB6223VB.....	245, 526	TF1816VB.....	496	TFAT9362VA.....	463	TRG5105OZ.....	93
SW2016X.....	535	TF1846TIB.....	505	TFAV1714VB.....	501	TRG8701OZ.....	95, 319
		TF1848TIB.....	504	TBFB348VB.....	262, 483	TT8604BN.....	364
		TF1850TIB.....	495	TBFB9362VB.....	483	TT8742BN.....	364
		TF1851TIB.....	491	TFCB6325VB.....	504	TT8743BN.....	364
TB8601C.....	365	TF1860FZ.....	488	TFCC8802.....	320, 506	TU8602BNLED.....	337
TB8602C.....	365	TF1860TZ.....	488	TFF16191A5VA.....	466	TU8603BNLED.....	337

T

TU8604BNLED.....	337
TVN1717DK.....	120, 250, 299
TVN232DK.....	120, 121, 250, 256
TVN5005DK.....	120, 250
TY1404AN.....	90, 316
TY1444AN.....	91, 316
TY1444WT.....	90, 316
TY1716AN.....	90, 298
TY1721AN.....	90, 298
TY43625AN.....	89, 91, 366, 530
TY5005AN.....	87, 88
TY628AN.....	90, 261
TY8501AN.....	87, 89, 319
TY8601AN.....	91, 319, 367
TY8601BN.....	91, 319, 367
TY8601C.....	91, 319, 367
TY8602AN.....	91, 367
TY8602BN.....	91, 367
TY8602C.....	91, 367
TY8602WT.....	91, 367
TY8603AN.....	91, 366, 367
TY8603BN.....	91, 367
TY8603C.....	91, 367
TY8603WT.....	91, 367
TY8604AN.....	91, 367
TY8604BN.....	91, 367
TY8604C.....	91, 367
TY8604WT.....	91, 367

U

UNS5204IB.....	169
UPCC5006IS.....	224
UPCN5006IS.....	221
UPCN5006WT.....	220, 221
UPCN5008IS.....	221
UPCN5008WT.....	221
UPEV5005WT.....	217
UPEV8701WT.....	216, 217, 320
UPFT1820IS.....	224, 276
UPHL8701IS.....	226, 320
UPMM5005WT.....	222, 223
UPMM8701WT.....	222, 223, 320
UPPS1510BN.....	225, 286
UPPS1510WT.....	225, 286
UPPS1713BN.....	225, 301
UPPS1713WT.....	225, 301
UPPS2813BN.....	225, 276
UPPS2813WT.....	225, 276
UPRZ43426C.....	219, 532
UPRZ53426C.....	219, 532
UPSE8701WT.....	226, 320
UPTR1716WT.....	218, 301

UPTR5007WT.....	218
UPTR8701IS.....	218, 320
UPTR8701WT.....	218, 320
UST1505WT.....	140, 285
UST1716WT.....	140, 299
UST5003WT.....	138, 139
UST6127WT.....	140, 525

V

VLA1618C.....	185, 309
VLA2820C.....	185, 274
VVAM6130BN.....	511
VVAM6130PN.....	511
VVAM9362BN.....	511
VVAM9362PN.....	511
VVBT6220WT.....	510
VVBT9348WT.....	510
VVCS6332OI.....	510
VVCS9360OI.....	510
VVCS9556OI.....	510
VVKY6328BN.....	509
VVKY6328PN.....	509
VVKY9258BN.....	508
VVKY9258PN.....	508
VVKY9358BN.....	509
VVKY9358PN.....	509
VVKY9558BN.....	508
VVKY9558PN.....	508
VVKY9658BN.....	508
VVKY9658PN.....	508
VVSP9348BN.....	512
VVSP9348WT.....	512
VVTH9348AB.....	512
VVTH9348IB.....	512
VVWH9348IB.....	511
VYR5006ML.....	149
VYR5008ML.....	149
VYR5012ML.....	149
VYR5024ML.....	148

W

WDM5005WT.....	160, 251
WHI1716IS.....	100, 299
WHI5005IS.....	99, 100
WHI5009IS.....	97
WHI5012IS.....	96
WHI8701IS.....	97, 98, 319
WLR1506MB.....	135, 285
WLR1716MB.....	135, 299
WLR2820MB.....	135, 274
WLR5204MB.....	134
WLS1613PN.....	307

WLS1615PN.....	307
WSY5005IF.....	153
WSY5008IF.....	153
WSY5012IF.....	152
WV1716BN.....	290

Y, Z

YU8710IB.....	318
ZE1617K.....	239, 310
ZE1717K.....	239, 301
ZE2822K.....	239, 277
ZP8414MD.....	240, 458
ZP8418MD.....	240, 458

9006-9112

9006EXAN.....	534
9006EXBA.....	534
9006EXBN.....	534
9006EXC.....	534
9006EXCC.....	534
9006EXD.....	534
9006EXDC.....	534
9006EXDK.....	534
9006EXES.....	534
9006EXIB.....	534
9006EXIF.....	534
9006EXIN01.....	534
9006EXIS.....	534
9006EXK.....	534
9006EXK01.....	534
9006EXLN.....	534
9006EXMB.....	534
9006EXMC.....	534
9006EXML.....	534
9006EXMM.....	534
9006EXMN.....	534
9006EXOS.....	534
9006EXOZ1.....	534
9006EXPN.....	534
9006EXRC.....	534
9006EXRK.....	534
9006EXRS.....	534
9006EXTM.....	534
9006EXVA.....	534
9006EXVB.....	534
9006EXVG.....	534
9006EXWT.....	534
9007EXAN.....	535
9007EXBN01.....	535
9007EXC.....	535
9007EXCC.....	535
9007EXIS.....	535

9007EXMM.....	535
9007EXOS.....	535
9007EXPN.....	535
9007EXRK.....	535
9007EXVA.....	535
9007EXWT.....	535
9008EXAN.....	535
9008EXBN01.....	535
9008EXC.....	535
9008EXCC.....	535
9008EXIS.....	535
9008EXMM.....	535
9008EXOS.....	535
9008EXPN.....	535
9008EXRK.....	535
9008EXVA.....	535
9008EXWT.....	535
9012EXAN.....	534
9012EXBA.....	534
9012EXBN.....	534
9012EXC.....	534
9012EXCC.....	534
9012EXD.....	534
9012EXDC.....	534
9012EXDK.....	534
9012EXES.....	534
9012EXIB.....	534
9012EXIF.....	534
9012EXIN01.....	534
9012EXIS.....	534
9012EXK.....	534
9012EXK01.....	534
9012EXLN.....	534
9012EXMB.....	534
9012EXMC.....	534
9012EXML.....	534
9012EXMM.....	534
9012EXMN.....	534
9012EXOS.....	534
9012EXOZ1.....	534
9012EXPN.....	534
9012EXRC.....	534
9012EXRK.....	534
9012EXRS.....	534
9012EXTB.....	534
9012EXTM.....	534
9012EXVA.....	534
9012EXVB.....	534
9012EXVG.....	534
9012EXWT.....	534
9016EXPN.....	534
9106EXBN.....	535
9112EXBN.....	535

QUOIZEL®

Artisans in Lighting... since 1930

www.quoise.com

Corporate Headquarters

6 Corporate Parkway, Goose Creek, SC 29445
Phone: (843) 553-6700

Corporate Headquarters/ Customer Service


590 Old Willets Path, Hauppauge, NY 11788
Phone: (631) 273-2700 Fax: (631) 231-7102
Toll-Free Consumer Hotline: 800-645-3184

Showroom – Dallas Trade Mart

3rd Floor, Space 3200, Dallas TX 75207
Phone: (214) 747-3665

Showroom – High Point Market

Showplace 3515
211 E. Commerce Ave., High Point NC 27260



\$10.00 CQ2017X

Printed in Canada. © 2016 Quoizel, Inc.