



2016 AT-A-GLANCE  
**LANDSCAPE  
LIGHTING**

**KICHLER®**

# THE BEST MEMORIES HAPPEN AFTER THE SUN GOES DOWN


Let your landscape lighting illuminate every occasion and invite people into your home safely and beautifully – highlighting walkways, architectural elements, gathering spaces, water features and more. A landscape lighting professional can show you all of the possibilities and deliver the best, most efficient lighting to bring your home to life.

## PERSONALIZED TO YOUR HOME – AND YOUR LIFESTYLE.

Your contractor will work with you to create a landscape lighting design that not only enhances your property, but also works with the way you use, live in, and enjoy your outdoor spaces. Consider your answers to these questions when creating your landscape lighting wish list:

- What do I love the most about my yard?
- How do I see myself using my outdoor spaces?
- When am I in these spaces most often?
- Is there a special architectural structure or feature that I want to highlight?
- When and where is security lighting most important?





Kichler Landscape Lighting offers some of the most technologically advanced products available. Leading the way is our integrated LED line, a complete system designed to give your landscape lighting professional a comprehensive toolbox of products, ideas and resources for your home's lighting plan. These fixtures, as well as our decorative outdoor lights, are engineered and tested to perform under extreme environmental conditions and are backed by our industry-leading 15 year warranty.

To learn more visit [www.kichler.com/landscape](http://www.kichler.com/landscape)

# DESIGN PRO INTEGRATED LED KICHLER TECHNOLOGY

A Kichler Design Pro Integrated LED lighting system offers long-term beauty and industry-leading technology that brings outdoor living spaces to life with best-in-class performance, quality and efficiency. Integrated Design with Fully Encapsulated Electronics for Optimal All-Weather Performance.



## PERFORMANCE

All Design Pro LED fixtures deliver beautiful lighting effects and are engineered for optimum performance with integrated solid-state drivers that are fully potted and sealed against the elements.

## VERSATILITY

Kichler's integrated LED portfolio includes decorative path & spread, hardscape, water feature, deck and accent lighting.

## INSTALLATION EASE

Our unique 9v to 15v operating range virtually eliminates voltage drop resulting in consistent light distribution without tricky calculations.


## EFFICIENCY

Design Pro LED lighting generates more lumens with less wattage – creating greater lighting effects while consuming less electricity.

3 part silicone moisture barrier and epoxy glass seal

Radiax™ custom formed highly reflective, parabolic optics generate high total lumens and maximum lumens per watt

3 part potting process ensures all air is removed, no voids.



On the light engine and all other electrical components. Warranty subject to change without notice. Visit [www.kichler.com](http://www.kichler.com) for full warranty and limitations.

# A LIGHT'S COLOR SETS THE TONE.

## LIGHTING DESIGN TIPS

Did you know that not all white light is created equal? Many of our integrated LED fixtures and LED replacement lamps come in a variety of color temperatures – from warm white to pure white to cool white – that can enhance the colors in your home’s exterior and landscape. Known as Kelvin (K) temperature, consider these suggestions for placement:



### WARM WHITE (2700K)

- Surroundings with warmer colors, like brown and cedar
- Natural-colored walls or stonework
- Foliage that is red, orange or yellow (ex: highlighting oak trees)



### PURE WHITE (3000K)

- Surroundings with dark materials, like deep slate, black or grey
- Foliage that is blue or purple (ex: highlighting blue spruce trees)



### COOL WHITE (4200K)

- Ultra contemporary homes and structures
- Commercial applications
- 120V only

## BEAM SPREADS...CARRY LIGHT WHERE IT'S NEEDED.


Kichler Design Pro LED Lights are available in a variety of beam spreads that allow your lighting professional to tailor the light to the application – creating the perfect end effect.




Tall, thin beam of light ideal for grazing trees and column features.



Medium height and width beam of light suited for general accent lighting.




Short and wide beam of light useful for broad trees and wide structures.



Ideal for wall washing, grazing, and short yet wide objects.

# LIGHTING TECHNIQUES



**ACCENT** creates scenes mimicking the natural affects of moonlight within trees or highlights architectural feature of your property



**ACCENT UPLIGHTING** shines light upward to illuminate an object or surface for dramatic, attention-getting visuals

Shown: 16070 LED Wall Wash – 3000K  
15384 Mini Accent with LED Drop-In Lamp – 3000K



**GRAZING** will add depth and dimension to stucco, brick, stonework or architectural features of your home or building

Shown: 16004 LED Radiax – 3000K  
15843 LED Path – 3000K

# LIGHTING TECHNIQUES



**SHADOWING** is used to project the look of a tree or your favorite yard art onto a surface behind the object

**SILHOUETTE LIGHTING** calls out an interesting shape by lighting a vertical surface behind the object to accent a unique shape

Shown: 16007 Radiax – 2700K






**MIRROR LIGHTING** is used to create dream-like water scenes by strategically lighting background areas around bodies of water

## LED LAMPS

Designed to fit landscape, outdoor and security lighting fixtures for both 12V and 120V systems, Kichler LED lamps offer superior cost savings and uncompromised performance. Available in a variety of lamp types, beam spreads and lumen options, Kichler LED lamps are the perfect fit to upgrade an existing incandescent system.

- Quality and consistent light output & beam spreads
- Potted and/or coated electronics to protect against moisture
- FCC Compliant
- Range of beam spread choices and Kelvin color temperature options (12V available in 2700K or 3000K. 120V available in 3000K or 4200K.)



# ACCENT LIGHTING

Dramatically focus attention to trees, yard art, architectural features, outdoor walkways, gardens and more.

## FEATURES:

- Multiple lumen outputs offer total design flexibility

## LED OPTIONS:

- 10°, 35°, 60°, 120° (Wall Wash) beam spreads
- Warm White 2700K or Pure White 3000K



ACCENT LIGHTING

# IN-GROUND LIGHTING


Deliver light to permanent and semi-permanent installations such as sidewalks, large mature trees, walls and flagpoles.

## LED FEATURES:

- Corrosion-free all brass construction – stronger than aluminum or composite

## LED OPTIONS:

- 10°, 35° or 60° beam spreads
- Warm White 2700K or Pure White 3000K



IN-GROUND LIGHTING

# UNDERWATER & WATER ACCENT

## LIGHTING


Enhance and highlight flowing water in waterfalls, streams and fountains. Create a magical mirroring affect on still waters, like ponds and pools.

### LED FEATURES:

- Rugged construction sealed against the elements for full submersion applications
- Rugged stainless steel housing with integral cowl

### LED OPTIONS:

- 60° beam spread
- Warm White 2700K or Pure White 3000K or Cool White 4200K



# PATH & SPREAD

## LIGHTING

Illuminate sidewalks, stone pathways and lawn walkways while adding a hint of intrigue to boulders and plant beds.

### LED FEATURES:

- Sealed/integrated, moisture-proof design
- Directs light in a smooth even 10' – 12' spread with little glare or drastic cutoff
- Classic designs with a wide variety of finish options
- Durable cast construction



PATH & SPREAD LIGHTING

# DECK & PATIO

## LIGHTING

Accentuate all of the beauty and detail of your deck, patio, outdoor kitchen, steps, handrails and more.

### FEATURES:

- Multiple architectural styles and finishes highlight the setting and add safety and security
- Weather tested to withstand the elements for years

### LED OPTIONS:

- Deck & Patio: Pure White 3000K or Warm White 2700K



DECK & PATIO LIGHTING

# HARDSCAPE LIGHTING

Highlight your stone features, retaining walls, outdoor kitchens, steps, handrails, benches and more.

## LED FEATURES:

- Available in multiple Kelvin temperature options: Warm White 2700K or Pure White 3000K
- Available in 1, 3, 6, and 9 LED fixtures
- Long-life LED light source — 40,000 hours at industry standard L70
- Tested to withstand the elements for years of enjoyment
- Easy to install



HARDSCAPE LIGHTING

# DESIGN PRO LED 12V ACCENT



**3W**

**10°**  
Beam Spread

SKU/  
Finish

**16000 AZT27** 16000 AZT30  
16000 BBR27 16000 BBR30  
16000 BKT27 16000 BKT30

Wattage

3W, 4VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 109 Lm 3000K – Pure White/ 116 Lm



**3W**

**35°**  
Beam Spread

SKU/  
Finish

16001 AZT27 16001 AZT30  
16001 BBR27 16001 BBR30  
**16001 BKT27** 16001 BKT30  
16001 WHT27 16001 WHT30

Wattage

3W, 4VA 12V LED

2700K – Warm White/ 109 Lm

3000K – Pure White/ 116 Lm



**3W**

**60°**  
Beam Spread

SKU/  
Finish

16002 AZT27 16002 AZT30  
16002 BBR27 16002 BBR30  
**16002 BKT27** 16002 BKT30

Wattage

3W, 4VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 109 Lm 3000K – Pure White/ 116 Lm



**4W**

**10°**  
Beam Spread

SKU/  
Finish

16003 AZT27 16003 AZT30  
16003 BBR27 16003 BBR30  
**16003 BKT27** 16003 BKT30

Wattage

4W, 5.5VA 12V LED

2700K – Warm White/ 151 Lm

3000K – Pure White/ 180 Lm



**4W**

**35°**  
Beam Spread

SKU/  
Finish

**16004 AZT27** 16004 AZT30  
16004 BBR27 16004 BBR30  
16004 BKT27 16004 BKT30  
16004 WHT27 16004 WHT30

Wattage

4W, 5.5VA 12V LED

2700K – Warm White/ 151 Lm

3000K – Pure White/ 180 Lm



**4W**

**60°**  
Beam Spread

SKU/  
Finish

16005 AZT27 16005 AZT30  
16005 BBR27 16005 BBR30  
**16005 BKT27** 16005 BKT30

Wattage

4W, 5.5VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 151 Lm 3000K – Pure White/ 180 Lm



**6.5W**

**10°**  
Beam Spread

SKU/  
Finish

**16006 AZT27** 16006 AZT30  
16006 BBR27 16006 BBR30  
16006 BKT27 16006 BKT30

Wattage

6.5W, 10.0VA 12V LED

2700K – Warm White/ 306 Lm

3000K – Pure White/ 352 Lm



**6.5W**

**35°**  
Beam Spread

SKU/  
Finish

16007 AZT27 16007 AZT30  
16007 BBR27 16007 BBR30  
**16007 BKT27** 16007 BKT30  
16007 WHT27 16007 WHT30

Wattage

6.5W, 10.0VA 12V LED

2700K – Warm White/ 306 Lm

3000K – Pure White/ 352 Lm



**6.5W**

**60°**  
Beam Spread

SKU/  
Finish

16008 AZT27 16008 AZT30  
**16008 BBR27** 16008 BBR30  
16008 BKT27 16008 BKT30

Wattage

6.5W, 10.0VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 306 Lm 3000K – Pure White/ 352 Lm



**13W**

**10°**  
Beam Spread

SKU/  
Finish

**16009 AZT27** 16009 AZT30  
16009 BBR27 16009 BBR30  
16009 BKT27 16009 BKT30

Wattage

13W, 18.5VA 12V LED

2700K – Warm White/ 520 Lm

3000K – Pure White/ 590 Lm



**13W**

**35°**  
Beam Spread

SKU/  
Finish

16010 AZT27 16010 AZT30  
**16010 BBR27** 16010 BBR30  
16010 BKT27 16010 BKT30  
16010 WHT27 16010 WHT30

Wattage

13W, 18.5VA 12V LED

2700K – Warm White/ 520 Lm

3000K – Pure White/ 590 Lm





**13W**

60°  
Beam Spread

SKU/  
Finish

16011 AZT27  
16011 BBR27  
**16011 BKT27**

16011 AZT30  
16011 BBR30  
16011 BKT30

Wattage

13W, 18.5VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 520 Lm    3000K – Pure White/ 590 Lm



**21W**

10°  
Beam Spread

**16012 AZT27**  
16012 BBR27  
16012 BKT27

16012 AZT30  
16012 BBR30  
16012 BKT30

21W, 27.0VA 12V LED

2700K – Warm White/ 947 Lm    3000K – Pure White/ 993 Lm



**21W**

35°  
Beam Spread

16013 AZT27  
**16013 BBR27**  
16013 BKT27  
16013 WHT27

16013 AZT30  
16013 BBR30  
16013 BKT30  
16013 WHT30

21W, 27.0VA 12V LED

2700K – Warm White/ 947 Lm    3000K – Pure White/ 993 Lm



**21W**

60°  
Beam Spread

SKU/  
Finish

16014 AZT27  
16014 BBR27  
**16014 BKT27**

16014 AZT30  
16014 BBR30  
16014 BKT30

Wattage

21W, 27.0VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 947 Lm    3000K – Pure White/ 993 Lm



**4.5W**

**15731 AZT, BBR, BKT** – 10° Spot  
15732 AZT, BBR, BKT – 35° Flood  
15733 AZT, BBR, BKT – 60° Wide Flood

4.5W, 7.5VA 12V LED

3000K – Pure White/150 Lm



**8.5W**

**15741 AZT, BBR, BKT** – 10° Spot  
15742 AZT, BBR, BKT – 35° Flood  
15743 AZT, BBR, BKT – 60° Wide Flood

8.5W, 12.2VA 12V LED

3000K – Pure White/310 Lm



**12.4W**

SKU/  
Finish

**15751 AZT, BBR, BKT** – 10° Spot  
15752 AZT, BBR, BKT – 35° Flood  
15753 AZT, BBR, BKT – 60° Wide Flood

Wattage

12.4W, 16.7VA 12V LED

Kelvin/  
Lumens

3000K – Pure White/460 Lm



**4.3W**

Wall Wash

16070 AZT27R    16070 AZT30R  
**16070 BBR27R**    16070 BBR30R  
16070 BKT27R    16070 BKT30R

4.3W, 5.8VA 12V LED

2700K – Warm White/ 294 Lm    3000K – Pure White/ 302 Lm



**4.3W**

Wall Wash

15861 AZT27R    15861 AZT30R  
**15861 BBR27R**    15861 BBR30R  
15861 BKT27R    15861 BKT30R

4.3W, 5.8VA 12V LED

2700K – Warm White/ 294 Lm    3000K – Pure White/ 302 Lm



DESIGN PRO LED  
12V  
IN-GROUND



**4W**

SKU/  
Finish

**16030 BBR27** – 10° Spot  
16030 BBR30 – 10° Spot  
16031 BBR27 – 35° Flood  
16031 BBR30 – 35° Flood  
16032 BBR27 – 60° Wide Flood  
16032 BBR30 – 60° Wide Flood

Wattage

4W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 146 Lm    3000K – Pure White/ 170 Lm



**6.5W**

**16033 BBR27** – 10° Spot  
16033 BBR30 – 10° Spot  
16034 BBR27 – 35° Flood  
16034 BBR30 – 35° Flood  
16035 BBR27 – 60° Wide Flood  
16035 BBR30 – 60° Wide Flood

6.5W, 9.3VA 12V LED

2700K – Warm White/ 306 Lm    3000K – Pure White/ 348 Lm

DESIGN PRO LED  
12V IN-  
GROUND  
CONTINUED



**14W**

SKU/  
Finish

**16036 BBR27** – 10° Spot  
**16036 BBR30** – 10° Spot  
**16037 BBR27** – 35° Flood  
**16037 BBR30** – 35° Flood  
**16038 BBR27** – 60° Wide Flood  
**16038 BBR30** – 60° Wide Flood

Wattage

14W, 18.5VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 520 Lm  
3000K – Pure White/ 590 Lm

**4.5W**

**15767 BKT** – 10° Spot  
**15768 BKT** – 35° Flood  
**15769 BKT** – 60° Wide Flood

4.5W, 7.5VA 12V LED

3000K – Pure White/150 Lm



**8.5W**

SKU/  
Finish

**15728 BKT** – 10° Spot  
**15747 BKT** – 35° Flood  
**15748 BKT** – 60° Wide Flood

Wattage

8.5W, 12.2VA 12V LED

Kelvin/  
Lumens

3000K – Pure White/310 Lm



**12.4W**

**15729 BKT** – 10° Spot  
**15757 BKT** – 35° Flood  
**15758 BKT** – 60° Wide Flood

12.4W, 16.7VA 12V LED

3000K – Pure White/460 Lm

DESIGN PRO LED  
12V 2-IN-1  
WATER  
ACCENT



**3.4W**

60°  
Beam Spread

SKU/  
Finish

**15711 SS27** – 2700K  
**15711 SS** – 3000K  
**15711 SS42** – 4200K

Wattage

3.4W, 4.9VA 12V LED

Kelvin/  
Lumens

2700K – 135 Lm  
3000K – 150 Lm  
4200K – 180 Lm



**15778 BK**  
One prong underwater  
light accessory



**15777 SS**  
Stainless steel easy  
mount bracket



**15776 BK**  
Three pronged  
underwater accessory

# DESIGN PRO LED 12V PATH & SPREAD



**3.8W**

SKU/  
Finish

**15843 CO27**  
15843 TZT27

15843 CO30  
15843 TZT30

Wattage

3.8W, 4.95VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/  
168 Lm      3000K – Pure White/  
182 Lm



**3.8W**

**15871 BBR27**  
15871 TZT27

15871 BBR30  
15871 TZT30

3.8W, 4.95VA 12V LED

2700K – Warm White/  
168 Lm      3000K – Pure White/  
182 Lm



**4.3W**

SKU/  
Finish

**15839 CO27R**  
15839 TZT27R

15839 CO30R  
15839 TZT30R

Wattage

4.3W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/  
294 Lm      3000K – Pure White/  
302 Lm



**4.3W**

**16120 AZT27**  
16120 BBR27  
16120 BKT27

**16120 AZT30**  
16120 BBR30  
16120 BKT30

4.3W, 5.8VA 12V LED

2700K – Warm White/  
294 Lm      3000K – Pure White/  
302 Lm



**4.3W**

SKU/Finish

**15850 CO27R**

15850 CO30R

Wattage

4.3W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/  
294 Lm      3000K – Pure White/  
302 Lm



**3.8W**

**15803 AZT27R**

15803 AZT30R

3.8W, 4.95VA 12V LED

2700K – Warm White/  
168 Lm      3000K – Pure White/  
182 Lm



**3.8W**

**15802 TZT27R**

15802 TZT30R

3.8W, 4.95VA 12V LED

2700K – Warm White/  
168 Lm      3000K – Pure White/  
182 Lm



**4.3W**

SKU/  
Finish

15800 AZT27R  
**15800 BBR27R**

15800 AZT30R  
15800 BBR30R

Wattage

4.3W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/  
294 Lm      3000K – Pure White/  
302 Lm



**4W**

**15833 AZT27R**

15833 AZT30R

4W, 5.8VA 12V LED

2700K – Warm White/  
126 Lm      3000K – Pure White/  
140 Lm



**1W**

**15804 AZT27R**

15804 AZT30R

1W, 1.7VA 12V LED

2700K – Warm White/  
126 Lm      3000K – Pure White/  
140 Lm



**4W**

SKU/  
Finish

**15805 BKT27R**

15805 BKT30R

Wattage

4W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/  
126Lm      3000K – Pure White/  
140 Lm



**4W**

**15806 BKT27R**

15806 BKT30R

4W, 5.8VA 12V LED

2700K – Warm White/  
126 Lm      3000K – Pure White/  
140 Lm



**4.3W**

15817 AZT27  
**15817 BN27**

15817 AZT30  
15817 BN30

4.3W, 5.8VA 12V LED

2700K – Warm White/  
294 Lm      3000K – Pure White/  
302 Lm



# DESIGN PRO LED 12V PATH & SPREAD

CONTINUED



**4.3W**

SKU/  
Finish

**15815 AZT27R**      **15815 AZT30R**  
15815 BKT27R      15815 BKT30R

Wattage

4.3W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 294 Lm      3000K – Pure White/ 302 Lm



**4.3W**

**15827 BBR27R**      15827 BBR30R

4.3W, 5.8VA 12V LED

2700K – Warm White/ 294 Lm      3000K – Pure White/ 302 Lm



**4.3W**

SKU/  
Finish

**15826 AZT27R**      **15826 AZT30R**  
**15826 BKT27R**      15826 BKT30R

Wattage

4.3W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 294 Lm      3000K – Pure White/ 302 Lm



**4.3W**

**15870 AZT27R**      15870 AZT30R  
15870 BBR27R      15870 BBR30R  
15870 BKT27R      15870 BKT30R

4.3W, 5.8VA 12V LED

2700K – Warm White/ 294 Lm      3000K – Pure White/ 302 Lm



**4.3W**

SKU/  
Finish

15810 AZT27R      15810 AZT30R  
**15810 BBR27R**      15810 BBR30R  
15810 BKT27R      15810 BKT30R

Wattage

4.3W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 294 Lm      3000K – Pure White/ 302 Lm



**4.3W**

**15811 AZT27R**      15811 AZT30R

4.3W, 5.8VA 12V LED

2700K – Warm White/ 294 Lm      3000K – Pure White/ 302 Lm



**3.8W**

15820 AZT27      15820 AZT  
15820 BBR27      15820 BBR  
**15820 CO27**      15820 CO

3.8W, 4.95VA 12V LED

2700K – Warm White/ 168 Lm      3000K – Pure White/ 182 Lm



**3.8W**

SKU/  
Finish

**15821 AZT27**      15821 AZT  
15821 BBR27      15821 BBR  
15821 CO27      15821 CO

Wattage

3.8W, 4.95VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 168 Lm      3000K – Pure White/ 182 Lm



**3.8W**

**15801 TZT27R**      15801 TZT30R

3.8W, 4.95VA 12V LED

2700K – Warm White/ 168 Lm      3000K – Pure White/ 182 Lm



**4.3W**

**16121 AZT27**      16121 AZT30  
16121 BKT27      16121 BKT30  
16121 TZT27      16121 TZT30

4.3W, 5.8VA 12V LED

2700K – Warm White/ 294 Lm      3000K – Pure White/ 302 Lm



**3.8W**

SKU/  
Finish

**16122 AZT27**      16122 AZT30

Wattage

3.8W, 4.95VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 168 Lm      3000K – Pure White/ 182 Lm

AZT Overlay with  
TZT Undertone



**3.8W**

16123 AZT27      16123 AZT30  
**16123 CO27**      16123 CO30  
16123 TZT27      16123 TZT30

3.8W, 4.95VA 12V LED

2700K – Warm White/ 168 Lm      3000K – Pure White/ 182 Lm



**3.8W**

**16124 AGZ27**      16124 AGZ30  
16124 BKT27      16124 BKT30  
16124 CW27      16124 CW30

3.8W, 4.95VA 12V LED

2700K – Warm White/ 168 Lm      3000K – Pure White/ 182 Lm



**4.3W**

SKU/  
Finish

**16125 AZT27** 16125 AZT30  
16125 BBR27 16125 BBR30  
16125 CO27 16125 CO30

Wattage

4.3W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 294 Lm 3000K – Pure White/ 302 Lm



AZT Overlay with  
TZT Undertone

**3.8W**

**16126 AZT27** 16126 AZT30

3.8W, 4.95VA 12V LED

2700K – Warm White/ 168 Lm 3000K – Pure White/ 182 Lm



**3.8W**

**15857 AZT27R** 15857 AZT30R

3.8W, 4.95VA 12V LED

2700K – Warm White/ 168 Lm 3000K – Pure White/ 182 Lm



**4.3W**

SKU/  
Finish

**15807 AZT27R** 15807 AZT30R  
15807 BBR27R 15807 BBR30R

Wattage

4.3W, 5.8VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 294 Lm 3000K – Pure White/ 302 Lm



**3.5W**

**16130 AZT28**  
16130 BKT28

3.5W, 5.67VA 12V LED

2800K – Warm White/Pure White 224 Lm



**3.5W**

**16131 AZT28**  
16131 BKT28

3.5W, 5.67VA 12V LED

2800K – Warm White/Pure White 224 Lm



**3.5W**

SKU/  
Finish

**16132 AZT28**  
16132 BKT28

Wattage

3.5W, 5.67VA 12V LED

Kelvin/  
Lumens

2800K – Warm White/Pure White 224 Lm



**3.5W**


**16133 AZT28**  
16133 BKT28

3.5W, 5.67VA 12V LED

2800K – Warm White/Pure White 224 Lm



# DESIGN PRO LED 12V DECK & PATIO



**.86W**

SKU/Finish	<b>15750 TZT27R</b>	15750 TZT30R
Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm



**.86W**

SKU/Finish	<b>15763 TZT27R</b>	15763 TZT30R
Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm



**.86W**

SKU/ Finish	<b>15765 AZT27R</b>	15765 AZT30R
	15765 BBR27R	15765 BBR30R
	15765 BKT27R	15765 BKT30R
	15765 WHT27R	15765 WHT30R
Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm



**.86W**

SKU/Finish	<b>15764 AZT27R</b>	15764 AZT30R
	15764 BBR27R	15764 BBR30R
	15764 WHT27R	15764 WHT30R
Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm



**.86W**

SKU/Finish	16110 AZT27	16110 AZT30
	16110 BBR27	16110 BBR30
	16110 BKT27	16110 BKT30
	16110 CO27	16110 CO30
	16110 GRY27	16110 GRY30
	<b>16110 SD27</b>	16110 SD30

Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm



**.86W**

SKU/Finish	<b>16111 AZT27</b>	16111 AZT30
	16111 BKT27	16111 BKT30
	16111 TZT27	16111 TZT30

Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm



**.86W**

SKU/Finish	<b>16112 AZT27</b>	16112 AZT30
------------	--------------------	-------------

Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm

AZT Overlay  
with TZT  
Undertone



**.86W**

SKU/Finish	<b>16113 AZT27</b>	16113 AZT30
	16113 CO27	16113 CO30
	16113 TZT27	16113 TZT30

Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm



15773



15774

**1.72W**

SKU/Finish	<b>15773 AZT27R</b>	15773 AZT30R
	<b>15774 AZT27R</b>	15774 AZT30R

Wattage	1.72W, 3.72VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 86 Lm	3000K – Pure White/ 82 Lm



15780



15782

**.86W**

SKU/Finish	<b>15780 AZT27R</b>	15780 AZT30R
	15780 BBR27R	15780 BBR30R
	15780 BKT27R	15780 BKT30R
	15780 CO27R	15780 CO30R
	15780 WHT27R	15780 WHT30R
	15782 AZT27R	15782 AZT30R
	15782 BBR27R	15782 BBR30R
	15782 BKT27R	15782 BKT30R
	<b>15782 CO27R</b>	15782 CO30R
	15782 WHT27R	15782 WHT30R

Wattage	.86W, 1.86VA 12V LED	
Kelvin/ Lumens	2700K – Warm White/ 43 Lm	3000K – Pure White/ 41 Lm

# DESIGN PRO LED 12V HARDSCAPE



## 0.19W

SKU/  
Finish

**15744 AZT27** 15744 AZT30  
15744 BBR27 15744 BBR30  
15744 CO27 15744 CO30  
15744 GRY27 15744 GRY30  
15744 SD27 15744 SD30  
15744 WHT27 15744 WHT30

Description/  
Wattage

1 LED Fixture with Bracket – 3.0" Length  
0.19W, 0.28VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 8.4 Lm 3000K – Pure White/  
8.6 Lm



## .75W

15745 AZT27 15745 AZT30  
15745 BBR27 15745 BBR30  
**15745 CO27** 15745 CO30  
15745 GRY27 15745 GRY30  
15745 SD27 15745 SD30  
15745 WHT27 15745 WHT30

3 LED Fixture with Bracket – 6.9" Length  
.75W, 1.3VA 12V LED

2700K – Warm White/ 34.7 Lm 3000K – Pure White/  
44.5 Lm



## 1.4W

SKU/  
Finish

**15746 AZT27** 15746 AZT30  
15746 BBR27 15746 BBR30  
15746 CO27 15746 CO30  
15746 GRY27 15746 GRY30  
15746 SD27 15746 SD30  
15746 WHT27 15746 WHT30

Description/  
Wattage

6 LED Fixture with Bracket – 12.9" Length  
1.4W, 2.4VA 12V LED

Kelvin/  
Lumens

2700K – Warm White/ 69.5 Lm 3000K – Pure White/  
88 Lm



## 2.2W

**15756 AZT27** 15756 AZT30  
15756 BBR27 15756 BBR30  
15756 CO27 15756 CO30  
15756 GRY27 15756 GRY30  
15756 SD27 15756 SD30  
15756 WHT27 15756 WHT30

9 LED Fixture with Bracket – 18.9" Length  
2.2W, 3.7VA 12V LED

2700K – Warm White/ 104.2 Lm 3000K – Pure White/  
132 Lm



## 0.19W

15734 AZT30  
**15734 BBR30**  
15734 CO30  
15734 GRY30  
15734 SD30  
15734 WHT30

1 LED Fixture without Bracket – 3" Length  
0.19W, 0.28VA 12V LED

3000K – Pure White/8.6 Lm



## .75W

SKU/  
Finish

15735 AZT30  
15735 BBR30  
15735 CO30  
15735 GRY30  
15735 SD30  
**15735 WHT30**

Description/  
Wattage

3 LED Fixture without Bracket – 6.9" Length  
.75W, 1.3VA 12V LED

Kelvin/  
Lumens

3000K – Pure White/44.5 Lm



## 1.4W

15736 AZT30  
15736 BBR30  
15736 CO30  
15736 GRY30  
**15736 SD30**  
15736 WHT30

6 LED Fixture without Bracket – 12.9" Length  
1.4W, 2.4VA 12V LED

3000K – Pure White/88 Lm



## 2.2W

15755 AZT30  
**15755 BBR30**  
15755 CO30  
15755 GRY30  
15755 SD30  
15755 WHT30

9 LED Fixture without Bracket – 18.9" Length  
2.2W, 3.7VA 12V LED

3000K – Pure White/132 Lm

### 1, 3, 6, & 9" LED Flat Mounting Bracket

**15716 SS**  
for use with  
15734, 15744



**15717 SS**  
for use with  
15735, 15745



**15718 SS**  
for use with  
15736, 15746



**15719 SS**  
for use with  
15755, 15756



# Design Pro LED Controller



SKU	<b>15DC100</b>
Description	100W LED Controller
Features	All-in-one power supply and controller provides personalization, versatility, and efficiencies to a professional LED installation  Height = 13.73" Depth = 4.46" Width = 8.62"



SKU	<b>15DC200</b>
Description	200W LED Controller
Features	All-in-one power supply and controller provides personalization, versatility, and efficiencies to a professional LED installation  Height = 13.71" Depth = 4.46" Width = 13.51"



SKU	<b>15DC300</b>
Description	300W LED Controller
Features	All-in-one power supply and controller provides personalization, versatility, and efficiencies to a professional LED installation  Height = 13.71" Depth = 4.46" Width = 13.51"



SKU	<b>16081WH</b>
Description	Controller – Range Extender
Features	Allows for wireless range extension (additional 300ft) between wireless devices (ex. power supply-to-power supply) Plugs into any standard 120V outlet (dry location).



SKU	<b>16080BK</b>
Description	Controller – Remote
Features	Allows the user to independently control lighting zones based on pre-defined programs. This enables the homeowner to temporarily override schedules on individual zones by turning the lights on/off at any given time. Can also be used a secondary programmer.



SKU	<b>16088BK, 16089BK</b>
Description	Controller – Wire
Features	Now 14 and 16 gauge direct burial wire can now be used with Kichler's Design Pro LED Controller. Available in 250' EZ Pull boxes for added convenience. To be used only with the Kichler Design Pro LED Controller. See Kichler DC voltage drop calculator to calculate wire runs.

Z-Wave is a registered trademark of Sigma Design and its subsidiaries in the United States and other countries. For recommended 3rd party accessories please consult Kichler for tested list.





# LED/INCANDESCENT 12V TRANSFORMERS

## RELIABLE

- Runs feature one common transformer per circuit. ANSI/UL1838 requirements limit each circuit to 300-W and 15V.
- Secondary circuit breakers offer short-circuit protection as a standard feature.
- Magnetic circuit breakers provide a faster response to a fault in the system.
- An in-line primary thermostat protects against thermal over-load. These built-in thermostats are auto-resetting, eliminating the need for replacement or maintenance.

## POWERFUL

- Various wattage options are available including: 60, 75, 100, 120, 200, 300, 600, 900, and 1200 in many options.
- Available in premium or economy options – convenient for larger, more complicated jobs or where smaller profile, lower-wattage units can be used.

## DURABLE

- Full enclosure of the housing protects components from weather, sprinkling systems and debris.
- Professional Series housings are made of stainless steel grade 304 designed to run cooler and resist corrosion and last longer in outdoor environments.

## WARRANTY

- Limited lifetime warranty offered on Stainless Steel (SS) transformer models.
- A limited 10-Year Warranty on powder-coated Textured Architectural Bronze™ (AZT) transformer models and in-ground models.

## CORE AND COIL CONSTRUCTION

All core and coil-types used in Kichler transformers, except economy series, feature epoxy encapsulation. This provides commercial-grade benefits such as:



High Efficient E.I. core and coil configuration is standard on most Kichler models



15PR75SS, 15PR900SS, 15PR1200SS, 15PL75AZT and 15PL900AZT feature high efficiency Toroid core and coil configuration



Name  
**PROFESSIONAL SERIES PR**  
Wattage  
100 – 1200W  
Description  
Output voltage taps 12/13/14/15 Volts



Name  
**PROFESSIONAL SERIES PR LED**  
Wattage  
75W  
Description  
Output voltage tap 15 Volts only for simplified LED installations



Name  
**PROFESSIONAL SERIES 2-IN-1 PR**  
Wattage  
2 x 300W  
Description  
2 separate sets of multi-tap output – 12V, 13V, 14V, 15V on each circuit



Name  
**PLUS SERIES PL**  
Wattage  
100 – 1200W  
Description  
Output voltage taps are 12/13/14/15 Volts, 80 Amp. Max. per board



Name  
**PLUS SERIES PL LED**  
Wattage  
75W  
Description  
Output voltage tap 15V only for simplified LED installations



Name  
**MANUAL SERIES M**  
Wattage  
100 – 600W  
Description  
Output voltage taps are 12V, 13V, 15V only on 15M300 AZT, and 15M600 AZT. 15M100AZT and 15M200 AZT are single 12V taps



Name  
**ECONOMY SERIES E**  
Wattage  
60W – 120W  
Description  
High and low voltage settings



Name  
**15IGT100 IN-GROUND SERIES**  
Wattage  
100W  
Description  
4 Taps (Multitaps)



Name  
**15IGT300 IN-GROUND SERIES**  
Wattage  
300W  
Description  
4 Taps (Multitaps) 12-15V



Name  
**15IGT600 IN-GROUND SERIES**  
Wattage  
600W  
Description  
Dual output – 8 Taps (Multitaps) 2 sets of 4 12-15V

## TRANSFORMER ACCESSORIES



15557 BK  
Mechanical  
Transformer  
Timer



15556 WH  
Digital  
Transformer  
Timer




15511 BK  
Synchronized  
Device



15565 BK  
Plug-In Transformer  
Cell



15534 BK  
Remote Plug-in  
Transformer Cell



# LED/INCANDESCENT 12V ACCENT



**SKU** 15384  
**Description** 12V LED Mini Accent  
**Finishes** AZT, AZT24, BKT, BKT24, CBR, CO  
**LED Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.  
**Options**



**SKU** 15484  
**Description** 12V LED Long Cowl Mini Accent  
**AZT** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.



**SKU** 15397  
**Description** 12V LED Architectural Grade Adjustable  
**Finishes** AZT  
**LED Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.  
**Options**



**SKU** 15398  
**Description** 12V LED Micro Accent – MR11  
**AZT** N/A



**SKU** 15309  
**Description** 12V LED Accent  
**Finishes** AZT, AZT 12, BKT  
**LED Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.  
**Options**



**SKU** 15374  
**Description** 12V LED Accent  
**Finishes** AZT, AZT 20L 24, BKT 20L 24  
**LED Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.  
**Options**



**SKU** 15382  
**Description** 12V LED Composite  
**BK** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.



**SKU** 15381  
**Description** 12V LED MR 16  
**Finishes** AZT, AZT 6, BBR, BKT  
**LED Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.  
**Options**



**SKU** 15475  
**Description** 12V LED Solid Brass  
**CBR** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.  
**Options**



**SKU** 15383  
**Description** 12V LED Bi-Pin  
**AZT** N/A



**SKU** 15390  
**Description** 12V LED Par 36  
**Finishes** AZT  
**LED Lamp** 11W (18021-18029) Compares to 50W Halogen.  
**Options**



**SKU** 15395  
**Description** 12V LED Adjustable Wide Flood  
**AZT** N/A



**SKU** 15396  
**Description** 12V LED Miniature Hooded Adjustable Wide Flood  
**AZT** N/A



**SKU**  
**15385**  
**Description** 12V LED Hooded Adjustable Wide Flood  
**Finishes** AZT  
**LED Lamp** N/A  
**Options**



**SKU**  
**15476**  
**Description** 12V LED Solid Brass Mini Wall Wash  
**Finishes** CBR  
**LED Lamp** 2W T5 Side Mount Wedge Base (18120-18121) Compares to 20W Halogen.



**SKU**  
**15361**  
**Description** 12V LED Adjustable Wall Wash  
**Finishes** AZT, BKT  
**LED Lamp** 2W S8 Wedge (18122-18123) Compares to 18.5W Krypton.



**SKU**  
**15387**  
**Description** 12V LED MR-16 Mini (Down) Wide Flood  
**Finishes** AZT  
**LED Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.



**SKU**  
**15093**  
**Description** 12V LED MR-16 Mini (Down)  
**Finishes** WHT  
**LED Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.



**SKU**  
**15494**  
**Description** 12V LED Long Cowl Mini  
**Finishes** AZT  
**LED Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.

## LED/INCANDESCENT 12V IN-GROUND



**SKU**  
**15088**  
**Description** 12V Yoke Held Par 36 Well  
**Finishes** BK, BK 12  
**Lamp** Use 15390 Lamps  
**Options**



**SKU**  
**15194**  
**Description** 12V Enclosed Par 36 In-Ground  
**Finishes** AZT  
**Lamp** Use 15390 Lamps



**SKU**  
**15190**  
**Description** 12V MR16 Mini In-Ground  
**Finishes** BK  
**Lamp** Use 15384 Lamps



**SKU**  
**15192**  
**Description** 12V MR16 Mini In-Ground with Cowl  
**Finishes** BK  
**Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.



**SKU**  
**15092**  
**Description** 12V MR16 Well  
**Finishes** BK  
**Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.




**SKU**  
**15481**  
**Description** 12V Solid Brass In-Ground with Frosted Lens  
**Finishes** CBR  
**Lamp** 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.

# LED/INCANDESCENT 12V WATER FEATURE



For use with a magnetic transformer combined with LED drop-in lamps, multiply fixture VA by the number of fixtures to determine size of the transformer. For use with the Design Pro LED Controller, multiply fixture watts by the number of fixtures to determine size of the controller. LED Fixtures are not for use with 3rd party electronic transformers. Subjected to Highly Accelerated Life Testing – 3rd party reliability testing.

SKU	<b>15191</b>
Description	12V LED Underwater
Finishes	<b>BK</b>
Incandescent Lamp	Power usage at 12V AC input VA MAX: 50-W(VA) MR-1635-W(VA) Max. MR-11 4W (18126-18133) Compares to 20W Halogen. 5W (18134-18141) Compares to 35W Halogen.
Options	



# LED/ INCANDESCENT 12V PATH & SPREAD



SKU	<b>15379</b>
Description	Gate House™
Finishes	<b>OZ</b>
LED Lamp	2W (18036-18038) Compares up to 18.5W Krypton.
Options	



SKU	<b>15447</b>
Description	Aries Manor™
Finishes	<b>OZ</b>
LED Lamp	2W (18039-18041) Compares up to 16W Xenon.
Options	



SKU	<b>15314</b>
Description	Single Tier Leaf
Finishes	<b>AZT, MST</b>
LED Lamp	2W (18036-18038) Compares up to 18.5W Krypton.
Options	



SKU	<b>15436</b>
Description	Intaglio Brass Crook Neck
Finishes	<b>OZ</b>
LED Lamp	2W (18039-18041) Compares up to 16W Xenon.
Options	



SKU	<b>15401</b>
Description	Thatched Roof
Finishes	<b>AZT</b>
LED Lamp	2W (18042-18044) Compares up to 20W Halogen.
Options	



SKU	<b>15369</b>
Description	Vintage Park™
Finishes	<b>TZT</b>
LED Lamp	2W (18036-18038) Compares up to 18.5W Krypton.
Options	



SKU	<b>15393</b>
Description	Kentucky
Finishes	<b>OZ</b>
LED Lamp	2W (18039-18041) Compares up to 16W Xenon.
Options	



SKU

**15426**

Description

Almeria™

Finishes

**OZ**

LED Lamp

2W (18039-18041) Compares up to 16W Xenon.

Options



SKU

**15422**

Description

Cotworld™

Finishes

**AGZ**

2W (18039-18041) Compares up to 16W Xenon.

Options



SKU

**15420**

Description

Cotworld™

Finishes

**AGZ**

2W (18039-18041) Compares up to 16W Xenon.

Options



SKU

**15421**

Description

Cotworld™ Convertible Height Tiki

Finishes

**AGZ**

LED Lamp

2W (18039-18041) Compares up to 16W Xenon.

Options



SKU

**15449**

Description

Cathedral Bollard

Finishes

**TZT**

2W (18039-18041) Compares up to 16W Xenon. 2W (18120-18121) Compares up to 16W Xenon.

Options



SKU

**15429**

Description

Cathedral

Finishes

**TZT**

2W (18039-18041) Compares up to 16W Xenon.

Options



SKU

**15457**

Description

Pierced Dome

Finishes

**AZT**

LED Lamp

2W (18039-18041) Compares up to 16W Xenon.

Options



SKU

**15437**

Description

Pierced Scrollwork

Finishes

**TZT**

2W (18039-18041) Compares up to 16W Xenon.

Options



SKU

**15330**

Description

Adjustable Crescent

Finishes

**OZ**

2W (18036-18038) Compares up to 18.5W Krypton. 2W (18122-18123) Compares up to 18.5W Krypton.

Options



SKU

**15443**

Description

Decorative Hammered Roof

Finishes

CO, OB, OB12, **TZT**

LED Lamp

2W (18036-18038) Compares up to 18.5W Krypton.

Options



SKU

**15471**

Description

Cast Hammered Roof

Finishes

**BBR, TZT**

2W (18036-18038) Compares up to 18.5W Krypton.

Options



SKU

**15418**

Description

Ribbed Roof

Finishes

**AZT**

2W (18042-18044) Compares up to 20W Halogen.

Options



SKU

**15349**

Description

Tulip

Finishes

**MST**

LED Lamp

2W (18036-18038) Compares up to 18.5W Krypton.

Options



SKU

**15313**

Description

Lafayette™ Lantern

Finishes

**TZG**

2W (18039-18041) Compares up to 16W Xenon.

Options



SKU

**15444**

Description

Larkin Estate™

Finishes

**OZ**

2W (18039-18041) Compares up to 16W Xenon.

Options

# LED/INCANDESCENT 12V PATH & SPREAD

CONTINUED

SKU

Description

Finishes  
LED Lamp  
Options



15350

Adjustable Copper

CO

N/A



15391

Zen Garden

OZ

2W (18039-18041) Compares up to 16W Xenon.



SKU

Description

Finishes  
LED Lamp  
Options

15392

Zen Garden Bollard

OZ

2W (18039-18041) Compares up to 16W Xenon. 2W (18120-18121) Compares up to 16W Xenon.



15319

Mission Lantern

PZ

2W (18036-18038) Compares up to 18.5W Krypton.



15429

Cathedral

TZT

2W (18039-18041) Compares up to 16W Xenon.



SKU

Description

Finishes  
LED Lamp  
Options

15322

Cross Creek™ Lantern

AGZ

2W (18039-18041) Compares up to 16W Xenon.



15458

Mission Bollard

OZ

2W (18039-18041) Compares up to 16W Xenon. 2W (18120-18121) Compares up to 16W Xenon.



15367

Round Lantern

TZT

2W (18036-18038) Compares up to 18.5W Krypton.



SKU

Description

Finishes  
LED Lamp  
Options

15438

Traditional Marine Lantern

OB, OZ

2W (18036-18038) Compares up to 18.5W Krypton.



15450

Mica Mission

TZT

N/A



15334

Concord Lantern

OB

2W (18039-18041) Compares up to 16W Xenon.



SKU

Description

Finishes  
LED Lamp  
Options

15317

Glass & Metal

AZT, BN

2W (18036-18038) Compares up to 18.5W Krypton.



15318

Galaxy

AZT

2W (18036-18038) Compares up to 18.5W Krypton.



15360

Simplicity Side Mount

AZT

2W (18036-18038) Compares up to 18.5W Krypton. 2W (18122-18123) Compares up to 18.5W Krypton.



SKU

**15333**

Description

Contours

Finishes  
LED Lamp  
Options

**TZT**

2W (18036-18038) Compares up to 18.5W Krypton.



**15439**

Fundamentals™

**CO, OB, TZT**

2W (18036-18038) Compares up to 18.5W Krypton.



**15328**

Larger Center Mount

**AZT**

2W (18036-18038) Compares up to 18.5W Krypton.



SKU

**15005**

Description

Fundamentals™

Finishes  
LED Lamp  
Options

**AZT, BKT**

2W (18036-18038) Compares up to 18.5W Krypton.



**15315**

Side Mount

**AZT, AZT6, BKT**

2W (18036-18038) Compares up to 18.5W Krypton. 2W (18122-18123) Compares up to 18.5W Krypton.



**15326**

Center Mount

**AZT, BKT**

2W (18036-18038) Compares up to 18.5W Krypton.



SKU

**15011**

Description

One Tier

Finishes  
LED Lamp  
Options

**AZT**

2W (18036-18038) Compares up to 18.5W Krypton.



**15336**

Large Eclipse™

**BKT, TZT**

2W (18036-18038) Compares up to 18.5W Krypton.



**15323**

Eclipse™

**AZT, BKT, TZT**

2W (18036-18038) Compares up to 18.5W Krypton.



SKU

**15423**

Description

Side Mount Eclipse™

Finishes  
LED Lamp  
Options

**AZT, BKT**

2W (18036-18038) Compares up to 18.5W Krypton. 2W (18122-18123) Compares up to 18.5W Krypton.



**15310**

Dome

**AZT, AZT6, BKT**

2W (18039-18041) Compares up to 16W Xenon.



**15410**

Dome

**AZT**

2W (18039-18041) Compares up to 16W Xenon.



SKU

**15470**

Description

6" Dome

Finishes  
LED Lamp  
Options

**AZT, BKT, CBR**

2W (18039-18041) Compares up to 16W Xenon.



**15480**

Solid Brass Missionary

**CBR**

2W G4/T3 Bi-Pin (18042-18044) Compares to 20W Halogen.



**15478**

Solid Brass Traditional

**CBR**

2W G4/T3 Bi-Pin (18042-18044) Compares to 20W Halogen.

# LED/INCANDESCENT 12V DECK & PATIO



SKU

**15047**

Description

Oak Trail™ Accent

Finishes

**OZ**

LED Lamp

N/A

Options



**15110**

Zen Garden™ Deck

**OZ**

N/A



SKU

**15071**

Description

Zen Garden™ Post

Finishes

**OZ**

LED Lamp

2W (18039-18041) Compares up to 16W Xenon.

Options

Xenon.



**15474**

Larkin Estate™ Post

**OZ**

2W (18039-18041) Compares up to 16W Xenon.

Xenon.



SKU

**15064**

Description

Half Moon

Finishes

AZT, **BBR**, WHT

LED Lamp

2W (18042-18044) Compares up to 20W Halogen.

Options

2W (18124-18125) Compares up to 20W Halogen.



**15065**

Mini

AZT, **BBR**, BKT, WHT

2W (18039-18041) Compares up to 16W Xenon.

2W (18120-18121) Compares up to 16W Xenon.

2W (18120-18121) Compares up to 16W Xenon.



**15045**

Full Back Mini Deck

**AZT**

2W (18039-18041) Compares up to 16W Xenon.

2W (18120-18121) Compares up to 16W Xenon.

2W (18120-18121) Compares up to 16W Xenon.



SKU

**15165**

Description

Mini Deck

Finishes

**AZT**

LED Lamp

2W (18039-18041) Compares up to 16W Xenon.

Options

2W (18120-18121) Compares up to 16W Xenon.



**15477**

Solid Brass Deck

**CBR**

2W T5 Side mount wedge base (18120-18121) Compares up to 16W Xenon.

2W T5 Side mount wedge base (18120-18121) Compares up to 16W Xenon.



**15077**

Adjustable Under Railing

**AZT**

2W (18036-18038) Compares up to 18.5W Krypton.

2W (18036-18038) Compares up to 18.5W Krypton.





SKU

**15066**

Description

6.5W Louvered Down

Finishes

**AZT, WHT**

LED Lamp

N/A

Options



**15079**

11.6W Up/Down Accent Light

**BBR**

2W (18039-18041) Compares up to 16W Xenon.



**15123**

35W Barbecue Light

**BKT**

N/A



SKU

**15070**

Description

11.6W Mini Step Light

Finishes

**AZT**

LED Lamp

2W (18120-18121) Compares up to 16W Xenon.

Options



**15072**

11.6W Mini Step Light

**AZT, WHT**

2W (18120-18121) Compares up to 16W Xenon.



**15074**

10W Louvered & Brick Light Glass Lens

**AZT**

2W (18124-18125) Compares up to 20W Halogen.



SKU

**15073**

Description

Louvered & Brick Light Glass Lens

Finishes

**AZT**

LED Lamp

2W (18124-18125) Compares up to 20W Halogen.

Options



**15409**

Zen Garden™ 12V Outdoor Chandelier

**OZ**

2W (18039-18041) Compares up to 16W Xenon.





**15402**

Outdoor Trail™ 12V Outdoor Chandelier

**OZ**


2W (18039-18041) Compares up to 16W Xenon.

# LED/INCANDESCENT 12V ACCESSORIES




For use with fixtures 4W, 6.5W & 14W –  
16030, 16031, 16032, 16033,  
16034, 16035, 16036, 16037,  
16038

SKU **16501**  
Description **Concrete Installation Kit**  
Finishes **BBRP**



1/4-18 NPSM thd. Stems 0.5" D. overall  
12" – 15651 AZT, 15651 BKT  
18" – 15652 AZT, 15652 BKT  
24" – 15653 AZT, 15653 BKT  
  
1/2-14 NPSM thd. Stems .75" D. overall  
6" – 15645 AZT, 15645 BBR, 15645 BKT  
12" – 15656 AZT, 15656 BBR, 15656 BKT  
18" – 15657 AZT, 15657 BBR, 15657 BKT  
24" – 15658 AZT, 15658 BBR, 15658 BKT


SKU **15645, 15651, 15652, 15653, 15656, 15657, 15658**  
Description **Fixture Mounting Stems**  
Finishes **AZT, BBR, BKT**



Extends from  
18" to 33"



4.0625" ID  
4.25" OD  
  
18" 15665 AZT, BKT  
24" 15666 AZT, BKT  
36" 15667 AZT, BKT




For use with  
LED fixtures  
16130AZT, 16130BKT,  
16131AZT, 16131BKT,  
16132AZT, 16132BKT,  
16133AZT, 16133BKT

SKU **15570**  
Description **Adjustable Height Stems**  
Finishes **AZT, BKT**

SKU **15665, 15666, 15667**  
Description **Bollard Mounting Kit**  
Finishes **AZT, BKT**

SKU **15671**  
Description **Bollard Template Kit**  
Finishes **ST**



23" Height

For use with  
LED fixtures  
16130AZT, 16130BKT,  
16131AZT, 16131BKT,  
16132AZT, 16132BKT,  
16133AZT, 16133BKT



8" Height –  
15575 In-Ground Stake  
  
14" Height –  
15576 In-Ground Stake



1.18" W  
2.09" H  
1.35" L



1/4-18 NPSM thd  
1.5" H

SKU **15578**  
Description **Bollard Mounting Stake**  
Finishes **BK**

SKU **15575, 15576**  
Description **Polymeric Support Stakes**  
Finishes **BK**

SKU **15647**  
Description **Elbow**  
Finishes **AZT, BBR, BKT**

SKU **15649**  
Description **Stem Coupler**  
Finishes **AZT, BBR, BKT**



4" D  
1/2-14 NPSM thd

SKU **15601**  
Description **Surface Mounting Flange**  
Finishes **AZT, BBR, BKT, WHT**



1" x 1/2-14  
NPSM thd

SKU **15602**  
Description **Flange Mounting Nipple**  
Finishes **AL**



1.5" x 2.5" x 1"  
1/2-14 NPSM thd

SKU **15607**  
Description **Surface Mounting Bracket**  
Finishes **AZT, BBR, BKT, WHT**



3.375" W  
15776 BK for use with 15711 SS

SKU **15776**  
Description **Multi-Fixture Weighted Base**  
Finishes **BK**



3.375" W  
15778 BK for use with 15711 SS

**15778**

Single Fixture Weighted Base

**BK**



2.52" W  
Use with fixture 15711 SS

**15777**

Out of Water Bracket

**SS**



2.39" W 2.31" W  
5.56" H 5.56" H

**15609**

Junction Box Mounting Bracket

**AZT, BKT, WHT**



**16064, 16065, 16066, 15875, 15876**

LED Amber Lens

**AMB**

16064 AMB for use with 3W & 4W – 16000, 16001, 16002, 16003, 16004, 16005

16065 AMB for use with 6.5W & 13W – 16006, 16007, 16008, 16009, 16010, 16011

16066 AMB for use with 21W – 16012, 16013, 16014

15875 AMB for use with 15731, 15732, 15733, 15741, 15742, 15743, 15767, 15768, 15769, 15728, 15747, 15748

15876 AMB for use with 15751, 15752, 15753, 15729, 15757, 15758



**16064, 16065, 16066, 15885, 15886**

LED Green Lens

**GRN**

16064 GRN for use with 3W & 4W – 16000, 16001, 16002, 16003, 16004, 16005

16065 GRN for use with 6.5W & 13W – 16006, 16007, 16008, 16009, 16010, 16011

16066 GRN for use with 21W – 16012, 16013, 16014

15885 GRN for use with 15731, 15732, 15733, 15741, 15742, 15743, 15767, 15768, 15769, 15728, 15747, 15748

15886 GRN for use with 15751, 15752, 15753, 15729, 15757, 15758



**16064, 16065, 16066, 15895, 15896**

LED Frosted Lens

**FRO**

16064 FRO for use with 3W & 4W – 16000, 16001, 16002, 16003, 16004, 16005

16065 FRO for use with 6.5W & 13W – 16006, 16007, 16008, 16009, 16010, 16011

16066 FRO for use with 21W – 16012, 16013, 16014

15895 FRO for use with LED fixtures 15731, 15732, 15733, 15741, 15742, 15743, 15767, 15768, 15769, 15728, 15747, 15748

15896 FRO for use with LED fixtures 15751, 15752, 15753, 15729, 15757, 15758



15875AMB

15886GRN

15895FRO

**15633 15643, 15672, 15676, 15691**

Incandescent Forsted Lens

**FRO**

15672 FRO for use with fixture 15382

15676 FRO for use with fixtures 15092, 15384, 15484, 15494

15691 FRO for use with fixture 15381

15643 FRO for use with fixture 15374

15633 FRO for use with fixture 15398



**15677, 15695**

Polycarbonate Lens

**CLR**

15677 CLR for use with fixture 15827

15695 CLR for use with fixture 15315, 15815



**15632, 15642, 15674, 15675, 15692**

LED Frosted Lens

**LIN**

15674 LIN clear ribbed for use with fixture 15382

15675 LIN clear ribbed for use with fixtures 15092, 15384, 15484, 15494

15692 LIN clear ribbed for use with fixture 15381

15642 LIN clear ribbed for use with fixture 15374

15632 LIN clear ribbed for use with fixture 15398



**15659, 15689**

Heat Resistant Lens

**AZT, BKT**

15659 AZT for use with fixture 15079

15689 BK for use with fixtures 15088, 15388



**15631, 15641, 15673, 15686, 15687, 15693**

Blue Lens

**BL**

15673 BL for use with fixture 15382

15686 BL for use with fixtures 15092, 15384, 15484, 15494

15687 BL for use with fixture 15381

15693 BL for use with fixture 15397

15641 BL for use with fixture 15374

15631 BL for use with fixture 15398



5.8"

**16060, 16062**

LED Long Cowl

**AZT, BBR, BKT, WHT**

16060 AZT, 16060 BBR for use with 6.5W & 13W fixtures 16061 BKT 16006, 16007, 16008, 16009, 16060 WHT 16010, 16011

16062 AZT, 16062 BBR, 16063 BKT for use with 21W fixtures 16062 WHT 16012, 16013, 16014



16061: 2.5"  
16063: 3.3"

**16061, 16063**

LED 360° Short Cowl

**AZT, BBR, BKT, WHT**

16061 AZT, 16061 BBR, 16061 BKT, 16061 WHT for use with 6.5W & 13W fixtures 16006, 16007, 16008, 16009, 16010, 16011

16063 AZT, 16063 BBR, 16063 BKT, 16063 WHT for use with 21W fixtures 16012, 16013, 16014

SKU

Description

Finishes

SKU

Description

Finishes

SKU

Description

Finishes

SKU

Description

Finishes

# LED/INCANDESCENT 12V ACCESSORIES

CONTINUED



**SKU** 16050  
**Description** Cowl – Polycarbonate/Cast Brass  
**Finishes** BBRP, BBR  
 16050 BBRP for use with 4W, 6.5W & 14W fixtures 16030, 16031, 16032, 16033, 16034, 16035, 16036, 16037, 16038



**SKU** 16051  
**Description** LED Rock Guard – Polycarbonate/Cast Brass  
**Finishes** BBRP, BBR  
 16051 BBRP for use with 4W, 6.5W & 14W fixtures 16030, 16031, 16032, 16033, 16034, 16035, 16036, 16037, 16038



**SKU** 15701, 15702, 15703, 15704  
**Description** LED Snap-On Cowls  
**Finishes** AZTP, BKTP  
 Short Cowl – 15701 AZTP for use with fixtures 15731, 15732, 15701 BKTP 15733, 15741, 15742, 15743  
 15702 AZTP for use with fixtures 15751, 15702 BKTP 15752, 15753  
 For BBR fixture finishes, use AZTP  
 Long Cowl – 15703 AZTP for use with fixtures 15731, 15732, 15703 BKTP 15733, 15741, 15742, 15743  
 15704 AZTP for use with fixtures 15704 BKTP 15751, 15752, 15753  
 For BBR fixture finishes, use AZTP




**SKU** 15787  
**Description** LED Rock Guard  
**Finishes** BK  
 15787 BK only for use with fixtures 15767BKT, 15768BKT, 15769BKT, 15728BKT, 15747BKT, 15748BKT, 15729BKT, 15757BKT, 15758BKT



**SKU** 15694  
**Description** Incandescent Rock Guard  
**Finishes** AZ  
 15694 AZ for use with fixture 15194 or 15268



**SKU** 15690  
**Description** Incandescent Rock Guard  
**Finishes** BK  
 15690 BK for use with fixtures 15088BK or 15388 BK



**SKU** 15679, 15680, 15683, 15644, 15634, FM127265  
**Description** Hexcell Louver  
**Finishes** BK  
 15679 BK for use with fixtures 15092, 15384, 15484, 15494  
 15680 BK for use with fixture 15381  
 15683 BK for use with fixture 15397  
 15644 BK for use with fixture 15374  
 15634 BK for use with fixture 15398 FM127265  
 For use with downward center mount LED path lights.



**SKU** 15482  
**Description** Solid Brass Rock Guard with Clear Glass  
**Finishes** CBR  
 15482 CBR for use with fixture 15481 CBR



Length = 3.93"  
 Width = 1.33"




**SKU** 16080  
**Description** Remote  
**Finishes** BK  
 16080BK Remote



Length = 1.83"  
 Width = 1.83"



**SKU** 16081  
**Description** Range Extender  
**Finishes** WH  
 16081WH Range Extender



SKU  
**15507**  
Description  
Kichler Landscape Flag Marker  
Finishes  
**ONG**



SKU  
**15670**  
Description  
Corrosion Preventative Compound  
Finishes  
**BK**



SKU  
**16059**  
Description  
Low Voltage Power Conditioner (LVPC)  
Finishes  
**BK**  
16059 BK Master pack of 5



SKU  
**15529**  
Description  
Pro Series Wire Connector  
Finishes  
**BL**  
15529 BL Bulk pack of 100 connectors packed in sealed bags of 10



SKU  
**15501, 15502, 15503, 15503, 15504, 15505, 15506**  
Description  
Low Voltage Cable  
Finishes  
**BKT**  
For use with all 12V rated fixtures.  
8-gauge – 15503 BK 250'  
10-gauge – 15504 BK 250'  
12-gauge – 15501 BK 100',  
15502 BK 250', 15505 BK 500',  
15506 BK 1000




SKU  
**15579, 15589**  
Description  
Gel Filled Wire Connector  
Finishes  
**BKT**  
15579 BK for use when connecting:  
• 8-gauge wire to 10- and 12-gauge  
• connecting 10-gauge wire to 12-gauge wire  
15589 BK for use when connecting:  
• 10-gauge wire  
• 12-gauge wire  
• 10-gauge wire to 12-gauge wire  
• 12-gauge wire to 18-gauge wire





SKU  
**15509**  
Description  
QUIC DISC Connector  
Finishes  
**BKT**  
15509 BK for use with #12-2 or #10-2 low voltage cable only



SKU  
**16081**  
Description  
Wire  
Finishes  
**BK**  
16088BK – #14-2 Wire,  
16089BK – #16-2 Wire




BASE / LAMP TYPE	WATTS	KELVIN / LUMENS	BEAM ANGLE
<b>S8 Wedge</b> 	2W, 2.4VA* Compares up to 18.5W Krypton	2700K – Warm White 130Lm	<b>120° BEAM ANGLE</b> 18122
		3000K – Pure White 130Lm	18123
<b>T5 Wedge</b> 	2W, 2.4VA* Compares up to 16W Xenon	2700K – Warm White 130Lm	18120
		3000K – Pure White 130Lm	18121
<b>G4/T3 Bi-Pin</b> 	2W, 2.4VA* Compares up to 20W Halogen	2700K – Warm White 130Lm	18124
		3000K – Pure White 130Lm	18125

\* Ideal for side mount path, deck/step, wall wash fixtures and more.  
 \* Multiply fixture VA by the number of fixtures used to determine size of transformer.  
 Stated lumens are for bare lamp only. Using lamp in enclosed fixtures can result in up to 30-40% loss in lumen output based on test data.

All lamps are listed or certified by UL, ETL, and/or CSA to the appropriate ANSI/standard for both the United States and Canada and have tested for FCC compliance, assuring they won't interfere with other home electronic devices. So, you don't have to worry about inadvertent interference.



# LED/INCANDESCENT 12V ACCESSORIES CONTINUED



BASE / LAMP TYPE	WATTS	KELVIN / LUMENS	BEAM ANGLE			
<b>MR16 Bi-Pin</b> Medium Power 	4W, 5.3VA* Compares up to 20W Halogen		<b>15° SPOT</b>	<b>25° WIDE SPOT</b>	<b>40° FLOOD</b>	<b>60° WIDE FLOOD</b>
		2700K – Warm White 270Lm	18126	18128	18130	18132
		3000K – Pure White 270Lm	18127	18129	18131	18133
<b>MR16 Bi-Pin</b> High Power 	5W, 6.6VA* Compares up to 35W Halogen					
		2700K – Warm White 360Lm	18134	18136	18138	18140
		3000K – Pure White 360Lm	18135	18137	18139	18141
<b>PAR36/AR111</b> Wet Location 	11W, 14.9VA* Compares up to 50W Halogen		<b>15° SPOT</b>	<b>25° WIDE SPOT</b>	<b>40° FLOOD</b>	
		2700K – Warm White 540Lm	18021	18024	18027	
		3000K – Pure White 600Lm	18022	18025	18028	
<b>S8 Wedge</b> 	2W, 2.8VA* Compares up to 18.5W Krypton		<b>300° OMNI-DIRECTIONAL</b>			
		2700K – Warm White 85Lm	18036			
		3000K – Pure White 100Lm	18037			
<b>T5 Wedge</b> 	2W, 2.8VA* Compares up to 16W Xenon		<b>300° OMNI-DIRECTIONAL</b>			
		2700K – Warm White 85Lm	18039			
		3000K – Pure White 100Lm	18040			
<b>G4/T3 Bi-Pin</b> 	2W, 2.8VA* Compares up to 20W Halogen		<b>300° OMNI-DIRECTIONAL</b>			
		2700K – Warm White 85Lm	18042			
		3000K – Pure White 100Lm	18043			

\* Multiply fixture VA by the number of fixtures used to determine size of transformer.

Stated lumens are for bare lamp only. Using lamp in enclosed fixtures can result in up to 30-40% loss in lumen output based on test data.

All lamps are listed or certified by UL, ETL, and/or CSA to the appropriate ANSI/standard for both the United States and Canada and have tested for FCC compliance, assuring they won't interfere with other home electronic devices. So, you don't have to worry about inadvertent interference.



# DESIGN PRO LED 120V ACCENT



**12.5W**

**10°**  
Beam Spread

SKU/  
Finish

16200 AZT30  
**16200 BBR30**  
16200 WHT30

16200 AZT42  
16200 BBR42  
16200 WHT42

Wattage

12.5W, 13VA 12V LED

Kelvin/  
Lumens

3000K – Warm White/  
590 Lm    4250K – Pure White/  
646 Lm



**12.5W**

**35°**  
Beam Spread

**16201 AZT30**  
16201 BBR30  
16201 WHT30

16201 AZT42  
16201 BBR42  
16201 WHT42

12.5W, 13VA 12V LED

3000K – Warm White/  
590 Lm    4250K – Pure White/  
646 Lm



**12.5W**

**60°**  
Beam Spread

SKU/  
Finish

16206 AZT30  
16206 BBR30  
**16206 WHT30**

16206 AZT42  
16206 BBR42  
16206 WHT42

Wattage

12.5W, 13VA 12V LED

Kelvin/  
Lumens

3000K – Warm White/  
590 Lm    4250K – Pure White/  
646 Lm



**19.5W**

**10°**  
Beam Spread

16202 AZT30  
**16202 BBR30**  
16202 WHT30

16202 AZT42  
16202 BBR42  
16202 WHT42

19.5W, 18VA 12V LED

3000K – Warm White/  
947 Lm    4250K – Pure White/  
993 Lm



**19.5W**

**35°**  
Beam Spread

SKU/  
Finish

**16203 AZT30**  
16203 BBR30  
16203 WHT30

16203 AZT42  
16203 BBR42  
16203 WHT42

Wattage

19.5W, 18VA 12V LED

Kelvin/  
Lumens

3000K – Warm White/  
947 Lm    4250K – Pure White/  
993 Lm



**19.5W**

**60°**  
Beam Spread

16207 AZT30  
16207 BBR30  
**16207 WHT30**

16207 AZT42  
16207 BBR42  
16207 WHT42

19.5W, 18VA 12V LED

3000K – Warm White/  
947 Lm    4250K – Pure White/  
993 Lm



**29W**

**10°**  
Beam Spread

16204 AZT30  
**16204 BBR30**  
16204 WHT30

16204 AZT42  
16204 BBR42  
16204 WHT42

29W, 27VA 12V LED

3000K – Warm White/  
1,131 Lm    4250K – Pure White/  
1,368 Lm



**29W**

**35°**  
Beam Spread

SKU/  
Finish

**16205 AZT30**  
16205 BBR30  
16205 WHT30

16205 AZT42  
16205 BBR42  
16205 WHT42

Wattage

29W, 27VA 12V LED

Kelvin/  
Lumens

3000K – Warm White/  
1,131 Lm    4250K – Pure White/  
1,368 Lm



**29W**


**60°**  
Beam Spread

16208 AZT30  
16208 BBR30  
**16208 WHT30**

16208 AZT42  
16208 BBR42  
16208 WHT42

29W, 27VA 12V LED

3000K – Warm White/  
1,131 Lm    4250K – Pure White/  
1,368 Lm



LED/INCANDESCENT  
120V ACCESS



SKU **15231**  
 Description 120V 35W Small  
 Finishes **AZT, BKT**  
 LED Lamp 7W PAR20 Wet (18081-18086) Compares up to 35W Halogen.  
 Options



SKU **15241**  
 Description 120V 70W Medium  
 Finishes **AZT, BKT**  
 LED Lamp 12W PAR30L Wet (18111-18116) Compares up to 50W Halogen.  
 Options



SKU **15231**  
 Description 120V 175W LED Large  
 Finishes **AZT, BKT**  
 LED Lamp 17W PAR38 Wet (18093-18098) Compares up to 75W Halogen.  
 Options



SKU **15230**  
 Description 120V 35W LED Small Compact  
 Finishes **AZT**  
 LED Lamp N/A  
 Options



SKU **15250**  
 Description 120V 100W LED Large Compact  
 Finishes **AZT**  
 LED Lamp 12W PAR30L Wet (18111-18116) Compares up to 50W Halogen.  
 Options



SKU **15255**  
 Description 120V 175W LED Downlight  
 Finishes **AZT**  
 LED Lamp 17W PAR38 Wet (18093-18098) Compares up to 75W Halogen.  
 Options



SKU **15295**  
 Description 120V 150W In-Ground Incandescent – PAR38  
 Finishes **AZ**  
 LED Lamp 17W PAR38 Wet (18093-18098) Compares up to 75W Halogen.  
 Options



SKU **15268**  
 Description 120V 75W Small In-Ground – PAR20/PAR30  
 Finishes **AZ**  
 LED Lamp 7W PAR20 Wet (18081-18086) Compares up to 35W Halogen.  
 Options 12W PAR30 Wet (18087-18029) Compares up to 50W Halogen.  
 12W PAR30L Wet (18111-18116) Compares up to 50W Halogen.



SKU **15262**  
 Description 120V 35W In-Ground 35-W MH  
 Finishes **AZ**  
 LED Lamp 7W PAR20 Wet (18081-18086) Compares up to 35W Halogen.  
 Options 12W PAR30 Wet (18087-18029) Compares up to 50W Halogen.  
 12W PAR30L Wet (18111-18116) Compares up to 50W Halogen.



SKU **15263**  
 Description 120V 170W In-Ground 70-W MH  
 Finishes **AZ**  
 LED Lamp 7W PAR20 Wet (18081-18086) Compares up to 35W Halogen.  
 Options 12W PAR30 Wet (18087-18029) Compares up to 50W Halogen.  
 12W PAR30L Wet (18111-18116) Compares up to 50W Halogen.



SKU **15266**  
 Description 120V 70W In-Ground 70-W MH Quad-Tap  
 Finishes **AZ**  
 LED Lamp 7W PAR20 Wet (18081-18086) Compares up to 35W Halogen.  
 Options 12W PAR30 Wet (18087-18029) Compares up to 50W Halogen.  
 12W PAR30L Wet (18111-18116) Compares up to 50W Halogen.



INCANDESCENT  
120V  
PATH  
& SPREAD



SKU  
Description  
Finishes  
Lamp  
Type

**15205**  
120V 75W Three Tier  
AZT, BKT  
Up to 75W Max. A19 light bulb  
(not supplied)

**15211**  
120V Large One Tier  
AZT, BKT  
Internal ANSI M98 Metal Halide ballast  
with 120V tap



SKU  
Description  
Finishes  
Lamp  
Type

**15232**  
120V 25W Cross Creek™ Lantern  
AGZ  
Up to 25W Max. A19 light bulb  
(not supplied)




**15236**  
120V 25W Eclipse™  
BKT, TZT  
Up to 25W Max. A19 light bulb  
(not supplied)



**15239**  
120V Traditional Marine Lantern  
OZ  
Up to 25W Max. A19 light bulb  
(not supplied)

LED/INCANDESCENT  
120V  
OUTDOOR



SKU  
Description  
Finishes  
Lamp  
Type

**11251**  
14.67W LED 120V Outdoor  
AZT, BKT  
Integrated high output Nichia LEDs  
and Drivers

**11250**  
11.23W LED 120V Outdoor  
AZT, BKT  
Integrated high output Nichia LEDs  
and Drivers



SKU  
Description  
Finishes  
Lamp  
Type

**11077**  
15.42W LED 120V Outdoor  
AZT, BKT  
Integrated high output Nichia LEDs  
and Drivers



**6051**  
120W 120V Outdoor  
AZ, WH  
12W PAR30 Wet (18087-18092) Compares  
up to 50W Halogen.  
12W PAR30L Wet (18111-18116) Compares  
up to 50W Halogen.  
17W PAR38 Wet (18093-18098) Compares  
up to 75W Halogen.



**6052**  
120W 120V Outdoor  
AZ, WH  
12W PAR30 Wet (18087-18092) Compares  
up to 50W Halogen.  
12W PAR30L Wet (18111-18116) Compares  
up to 50W Halogen.  
17W PAR38 Wet (18093-18098) Compares  
up to 75W Halogen.

# ADDRESS LIGHT KIT

The address light collection provides for enhanced visibility to your home address for deliveries, visitors and in emergency situations.



**43800 BKT**  
Xenon Address Light



**43800 OZ**  
Xenon Address Light



**43800 BKT LED**  
LED Address Light



**43800 OZ LED**  
LED Address Light



**4355 CLR**  
5W T5 Wedge Base



**4381**  
Transformer



**4301 - E**  
#1 Block



**4302 - F**  
#2 Block



**4303 - G**  
#3 Block



**4304 - H**  
#4 Block



**4305 - J**  
#5 Block



**4306 - K**  
#6 Block



**4307 - L**  
#7 Block



**4308 - M**  
#8 Block



**4309 - N**  
#9 Block



**4300 - O**  
#0 Block




**4310 - P**  
Blank Block



**4311 - Q**  
2 Blank  
Half Blocks

CAST ALUMINUM  
CONSTRUCTION

## INCANDESCENT 120V BALLASTS



SKU

**15MHS35**

Description

Above Ground

Finishes

**AZT**

Product ID - 15MHS35 AZT  
Description - Single 35-W-MH  
Tap - 120V  
ANSI# - M130



SKU

**15IGMHS70**

Description



In-Ground

Finishes

**AZ**

Product ID - 15IGMHS70 AZ  
Description - Single 70-W MH  
Tap - 120V  
ANSI# - M98

# LED/INCANDESCENT 120V ACCESSORIES



6" – 15645 AZT, 15645 BBR, 15645 BKT  
 12" – 15656 AZT, 15656 BBR, 15656 BKT  
 18" – 15657 AZT, 15657 BBR, 15657 BKT  
 24" – 15658 AZT, 15658 BBR, 15658 BKT

1/2-14 NPSM thd. stems  
 .75 dia. overall

SKU **15645, 15656, 15657, 15658**

Description **Fixture Mounting Stems**

Finishes **AZT**



SKU **15276**

Description **Power Post®**

Finishes **BK**

15276 BKT – for use with fixtures  
 15205 AZT, 15205 BKT, 15211 AZT,  
 15211 BKT, 15232 AGZ, 5236 BKT,  
 15236 TZ, 15239 OB & 15239 OZ

SKU **15578**

Description **Bollard Mounting Stake**

Finishes **BK**

15578 BK – for use with all bollard mounting  
 kits on 12V and 120V fixtures 15005, 15205,  
 15211



4" D  
 1/2-14 NPSM thd

SKU

**15601**

Description **Surface Mounting Flange**

Finishes **AZT, BBR, BKT, WHT**



1" x 1/2-14  
 NPSM thd

SKU **15602**

Description **Flange Mounting Nipple**

Finishes **AL**




2.39" W  
 5.56" H

SKU **15609**

Description **Junction Box Mounting Bracket**

Finishes **AZT, BKT, WHT**



SKU **15671**

Description **Bollard Template Kit**

Finishes **ST**



15616 WHT10 – 10 pack

SKU

**15616 WHT10**

Description **Gel Encapsulant**

Finishes **WHT**



7" D  
 5.19" H

SKU **15608**

Description **In-Ground Concrete Pour Kit**

Finishes **AZ**

15608 AZ for use with 15262,  
 15263, 15266, 15295, 151GT100,  
 151GT300, 151GT600



SKU **16065, 16066**

Description **LED Amber Lens**

Finishes **AMB**

16065 AMB for use with 12.5W –  
 16200, 16201, 16206  
 16066 AMB for use with 19.5W &  
 29W – 16202, 16203, 16204,  
 16205, 16207, 16208



SKU **16065, 16066**

Description **LED Green Lens**

Finishes **GRN**

16065 GRN for use with 12.5W –  
 16200, 16201, 16206  
 16066 GRN for use with 19.5W &  
 29W – 16202, 16203, 16204,  
 16205, 16207, 16208




SKU

**16065, 16066**

Description **LED Frosted Lens**

Finishes **FRO**

16065 FRO for use with 12.5W –  
 16200, 16201, 16206  
 16066 FRO for use with 19.5W &  
 29W – 16202, 16203, 16204,  
 16205, 16207, 16208




SKU **15623**

Description **Blue Lens Filter**

Finishes **BL**

15623 BL for use with 15231



SKU **15638**

Description **45° Hexcell Louver**

Finishes **BK**

15638 BKT for use with 15241

LED/INCANDESCENT  
120V  
ACCESSORIES  
CONTINUED



SKU

Description

Finishes

**16060, 16062**

LED Long Cowl

**AZT, BBR, WHT**  
16060 AZT, BBR, WHT for use with 12.5W fixtures 16200, 16201, 16206  
16062 AZT, BBR, WHT for use with 19.5W & 29W fixtures 16202, 16203, 16204, 16205, 16207, 16208



**16061, 16063**

LED 360° Short Cowl

**AZT, BBR, WHT**  
16061 AZT, BBR, WHT for use with 12.5W fixtures 16200, 16201, 16206  
16063 AZT, BBR, WHT for use with 19.5W & 29W fixtures 16202, 16203, 16204, 16205, 16207, 16208



SKU

Description

Finishes

**15688**

Rock Guard

**AZ**  
15688 AZ for use with 15263, 15264, 15265 and 15295



**15620**

PAR20 Medium Cowl

**AZT, BKT**  
15620 AZT, BKT for use with 15231



SKU

Description

Finishes

**15628**

PAR20 Long Cowl

**AZT, BKT**  
15628 AZT, BKT for use with 15231



**15640**

PAR30 Medium Cowl

**AZT, BKT**  
15640 AZT, BKT for use with 15241



**15648**

PAR30 Long Cowl

**AZT, BKT**  
15648 AZT, BKT for use with 15241



SKU

Description

Finishes

**15660**

PAR38 Medium Cowl

**AZT, BKT**  
15660 AZT, BKT for use with 15251, 15255



**15668**

PAR38 Long Cowl

**AZT**  
15668 AZT for use with 15251, 15255



**15630**

PAR20 Cowl

**AZ**  
15630 AZ for use with 15230



SKU

Description


Finishes

**15650**

PAR38 Cowl

**AZT**  
15650 AZT for use with 15250

# LED 120V – 277V LAMPS



BASE / LAMP TYPE	WATTS	KELVIN / LUMENS	BEAM ANGLE	
<b>PAR20 – Wet*** Location</b> 	7W Compares up to 35W Halogen		<b>25° SPOT</b>	<b>40° FLOOD</b>
		2700K – Warm White 310Lm	18081	18084
		3000K – Pure White 330Lm	18082	18085
		4200K – Cool White 350Lm	18083	18086
<b>PAR30 – Wet*** Location</b> 	12W Compares up to 50W Halogen		<b>25° SPOT</b>	<b>40° FLOOD</b>
		2700K – Warm White 580Lm	18087	18090
		3000K – Pure White 610Lm	18088	18091
		4200K – Cool White 640Lm	18089	18092
<b>PAR30 – Wet*** Location Longneck</b> 	12W Compares up to 50W Halogen		<b>25° SPOT</b>	<b>40° FLOOD</b>
		2700K – Warm White 580Lm	18111	18114
		3000K – Pure White 610Lm	18112	18115
		4200K – Cool White 640Lm	18113	18116
<b>PAR38 – Wet*** Location</b> 	17W Compares up to 75W Halogen		<b>25° SPOT</b>	<b>40° FLOOD</b>
		2700K – Warm White 800Lm	18093	18096
		3000K – Pure White 850Lm	18094	18097
		4200K – Cool White 900Lm	18095	18098

\*\*\*Wet location versions designed and listed for use in an enclosed or open fixture. Stated lumens are for bare lamp only. Using lamp in enclosed fixtures can result in up to 30-40% loss in lumen output based on test data.

# KICHLER OUTDOOR LANTERNS

Our newest outdoor lighting collections add curb appeal and architectural interest wherever you choose. They are designed to make a statement and made to shine in the harshest of elements.



# OUTDOOR/INDOOR CEILING FANS

Add a gentle breeze in your outdoor spaces with a Kichler Outdoor rated Ceiling Fan. Designed and constructed to withstand the elements, they are a perfect way to enhance your out of doors leisure and entertainment experiences.





Catalog No. K315  
Printed in USA 12.15  
14-LD-3177-171M  
© Copyright All rights reserved. Kichler.  
Customer Service: 1-866-814-7702  
[kichler.com/landscape](http://kichler.com/landscape)

**KICHLER.**