

OUTDOOR



HINKLEY

L I G H T I N G

“ENERGY EFFICIENT LIGHTING is a must for eco-conscious homeowners. Now that the options for LED lamping mimic the luminous feeling of incandescents, we no longer have to choose between beautiful light and energy efficiency.”

HEATHER GARRETT | HEATHER GARRETT INTERIOR DESIGN
DURHAM, NC



IDEACENTER

OUTDOOR



QUINCY 26150Z, PAGE 633

WELCOME HOME *to style*

The warm glow of a lantern perched outside the front door has welcomed people home for centuries. Look for a style that complements your exterior, reinforcing the architectural elements for a smart façade that yields ample curb appeal. Brightening the entrance and exit points of your home makes security sense too, by deterring unwanted visitors and ensuring a safe passageway when laden with packages, keys and mobile devices. Typical installations include one lantern (we recommend it appear approximately $\frac{1}{3}$ the height of your door from the street) or if space allows, two lanterns (about $\frac{1}{4}$ the size of the door) that are placed on either side to complement the entrance. For long porches that run the length of the home (lucky you!), consider placing a series of hanging lanterns to illuminate this area for a warm and inviting appearance.

“Being able to see outside at night is a wonderful way to enlarge the feeling of the size of the property. The exterior becomes an extension of the interior and helps create the multi-dimensional home.”

KATIE LYDON | KATIE LYDON INTERIORS
NEW YORK, NY

ALFRESCO ATTITUDE

EXPANDING YOUR ENVIRONMENT with outdoor lighting unifies the relationship between your home and your natural surroundings and guarantees your neighbors will stop and stare! Create a cohesive style statement and integrate different lighting techniques with lanterns complemented by landscape lighting options like Path, Accent, Spot and Deck & Step. This often requires research and expert recommendations regarding the layout and installation to ensure it's done properly. For more information on Hinkley Landscape Lighting, we have plenty of tips, guidelines and advice! See pages 746-747 at the end of the outdoor section for more information and a breakdown of all our landscape lighting research tools.

material matters

“The salt air in the low-country can be brutal, so it's crucial to consider lighting, furniture and fabrics that are going to withstand the different climates.”

GINGER BREWTON
GINGER BREWTON INTERIORS
CHARLESTON, SC



“Exterior lighting WITH A LARGE LANTERN AT THE ENTRY sets a great stage.”

HEATHER GARRETT
HEATHER GARRETT INTERIOR DESIGN
DURHAM, NC

TRELLIS 1435RB, PAGE 684 | HARDY ISLAND 18007MZ
HINKLEY LANDSCAPE LIGHTING CATALOG



REGENCY
BRONZE



AGED ZINC



STAINLESS
STEEL



SATIN BLACK

LET IT OUT

Thanks to advancements in technology, fashionable finishes are no longer confined indoors. Rigorously tested to withstand harsh environments, from sea salt to frigid air and relentless heat, we have developed

a wide palette of durable outdoor finishes in rich hues and bold shades. When paired with sophisticated glass and decorative reflectors, these finishes will ensure your outdoor lanterns look striking from every angle under the sun.

KEY WEST 2905RB, PAGE 708 | NEWPORT 2625DZ, PAGE 550 | SURF 2355SS, PAGE 600
SATURN 1905SK, PAGE 573



THE *OUTSIDERS*

— *Dolce Far Niente* —

THE SWEETNESS OF DOING NOTHING

Let the outdoors in by creating multi-dimensional exterior living spaces that blend the best of both worlds. By adding layers of outdoor lighting, you can craft defined areas to lounge and linger, day or night. Hanging and wall mounted lanterns will tastefully illuminate everything from lush landscaped walkways to chic chaises and cozy eating alcoves, balancing creature comforts with the call of the wild.

“AN OUTDOOR SPACE IS AN EXTENSION OF THE HOUSE AND MY FAVORITE PLACE TO ENTERTAIN. I LIKE TO MAKE IT AS COMFORTABLE AS POSSIBLE—LAYERS OF AMBIENT LIGHT, COMFORTABLE SEATING, THROW PILLOWS AND EVEN A RUG TO MAKE IT A SPECIAL SPACE.”

RACHEL REIDER | RACHEL REIDER INTERIORS
BOSTON, MA

A woman wearing sunglasses and a white and black floral dress stands in a white archway. The archway is part of a larger white structure with three small windows at the top. Three outdoor light fixtures are visible: one on the right side of the archway and two on the left side. The background consists of lush green trees under a clear blue sky.

BRIDGING

THE GAP BETWEEN

*style &
technology*

Eco-chic lighting is a reality! No longer constrained by minimalist designs that are often a necessary blueprint to accommodate the physics of LEDs, Hinkley's engineers have developed cutting edge Integrated LED light engines for use in a wide variety of our most popular decorative styles. In short: Hinkley has the largest offering of energy-efficient outdoor products in the industry! If you are

committed to an energy-efficient outdoor lighting plan, we've got you covered with everything from colonial to contemporary to coastal collections. Up-to-the-minute specs on everything from operating voltage, light color and incandescent equivalency are always available on hinkleylighting.com.

THE FRESH FACE OF EXTERIOR INTEGRATED LED

SEE HOW HINKLEY'S INTEGRATED LED LIGHT SOURCES FUNCTION AND FLATTER ANY FAÇADE DURING THE DAY AND INTO THE EVENING. LED light sources produce a consistent warm white light of 2700K and >90 CRI.

UNI



UNI

DAY UNI engines are round discs set into the top of a fixture, making them only slightly visible and leaving an open appearance.

LIGHT A fixture using a UNI engine shines light down, capturing the detail of the glass in the light pattern it produces.

LESM



LESM

DAY The LESM engine replaces a standard medium base socket with a frosted glass dome approximately half the size of a standard incandescent bulb.

LIGHT An LESM engine sits further down into the glass portion of the fixture, allowing for a spread of light that extends further out and up from the fixture.

CONSTRUCTION SIGHT

THE DESIGN OF EVERY HINKLEY FIXTURE begins and ends with an essential formula that calculates both form and function. Performance is paramount, so the construction process of our lanterns is subject to intense inspections and analyzed numerous times with special consideration given to the harsh conditions these beauties are exposed to. To ensure they stand the test of time, temperature and technical toil, Hinkley employs an exceptional on site ETL-rated laboratory to verify the superior aptitude of every single lantern.

While researching outdoor lighting, look for materials used in the construction like stainless steel, solid brass or cast aluminum for maximum durability. Pay attention to the glass, welding and ease of re-lamping—all of these point to a well-constructed fixture worth your investment.

a breath of FRESH AIR


Sometimes it's fun to break the rules! By placing lanterns inside your home that were originally created with styling and proportions appropriate for outdoor installation, you can shine a new light on an interior space. Bold silhouettes and unexpected finishes work to your advantage to create a fresh, modern design statement.

“AN OUTDOOR LANTERN WITH A TRADITIONAL SHAPE AND A MORE CONTEMPORARY LINE ALWAYS CATCHES MY EYE.”

COLLEEN MCGILL
MCGILL DESIGN GROUP
TORONTO, ONTARIO



ATLANTIS 1648TT, PAGE 583



THE HERITAGE COLLECTION | REVERE 1185SN, PAGE 536

Archival REVIVAL

HATS OFF TO THE HERITAGE COLLECTION, A CURATION OF TIME-HONORED DESIGNS DEEPLY ROOTED IN OUR ORIGIN AS AN OUTDOOR LANTERN COMPANY.

CLASSIC SILHOUETTES PAIRED WITH UPDATED FINISHES AND HIGH-QUALITY MATERIALS CREATE A TIMELESS STATEMENT OF STYLE.

Heritage
COLLECTION



LINCOLN 2468OZ, PAGE 525
ANCHORAGE 1855 DZ, PAGE 535



OUTDOOR COLLECTIONS

ANCHORAGE	534	MONDRIAN	670
ARIA	602	MONTAUK	530
ATLANTIS	582	MONTICELLO	736
AUGUSTA	734	NANTUCKET	540
BARRINGTON	733	NEW CASTLE	636
BELDEN PLACE	638	NEWPORT	550
BINGHAM	542	OXFORD	716
BOLLA	650	PEMBROOK	647
BRIGHTON	538	PLANTATION	694
BRYNMAR	692	PULLMAN	627
BURTON	554	PUTNEY BRIDGE	528
CALISTOGA	635	QUINCY	632
CAMELOT	718	RALEY	698
CAPE COD	640	RANDOLPH	674
CASA	690	REEF	648
CASCADE	592	REGAL	710
CASTELLE	616	REVERE	536
CEDAR HILL	664	RILEY	634
CHANDLER	558	SAN CLEMENTE	728
CHATFIELD	526	SATURN	572
CHERRY CREEK	658	SEDGWICK	532
CHESTERFIELD	722	SENATOR	723
CLAYTON	672	SHELTER	604
CLIFTON BEACH	740	SOLARA	612
CLIFTON PARK	742	SOLO	610
COLFAX	570	SORRENTO	688
CORDILLERA	620	STANTON	629
DISTRICT	590	STRATFORD	656
DORIAN	614	SULLIVAN	630
DRAKE	666	SURF	600
EDGEWATER	724	SUTCLIFFE	552
ELM	621	TAHOE	680
ENZO	678	THISTLEDOWN	654
FORUM	706	TITAN	588
FREEPORT	644	TRAFALGAR	712
HARBOR	560	TRELLIS	684
HOLBROOK	668	TUCKER	662
HUDSON	556	VENTO	598
KEY WEST	708	WABASH	714
KUBE	594	WESTWINDS	682
LEDGEWOOD	622	WINDSOR	702
LEX	597	YORK	546
LINCOLN	524	HINKLEY LANDSCAPE LIGHTING	746
LUCERNE	738	POSTS & PIER MOUNTS	748
LUNA	578		
LUNA STEP	744		
MANHATTAN	566		
MANOR HOUSE	720		

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

LINCOLN™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Lincoln defines classic design with authentic hinged doors and panels of clear seedy glass adding to the allure of this traditional cast aluminum lantern.



2465 OZ
10" W, 19" H



2462 OZ
8½" W, 16¾" H



2468 OZ
10" W, 23¼" H



2460 OZ
7½" W, 13¾" H



2464 OZ
8½" W, 16¾" H



2461 OZ
10" W, 21" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2460 OZ	1-100w Med.	8¾"	6½"	4½" W, 9" H Back Plate	
2461 OZ	3-60w Cand.			3" Dia. Post Fitter	
2462 OZ	2-60w Cand.			5" Dia. Canopy	6', 5'
2464 OZ	2-60w Cand.	10¼"	7¾"	4¾" W, 12¼" H Back Plate	
2465 OZ	3-60w Cand.	11¼"	8½"	4¾" W, 12¼" H Back Plate	
2468 OZ	3-60w Cand.	11¼"	13½"	4¾" W, 12¼" H Back Plate	

For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

CHATFIELD™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Chatfield delivers the finest in East Coast traditional style with generous panels of clear seedy glass, tiered candles and solid aluminum construction that features a mansard roof and authentic corner post finials.



2784 OZ
9" W, 18¼" H



2782 OZ
9" W, 20" H



2780 OZ
7" W, 14¼" H



2781 OZ
9" W, 20¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2780 OZ*	1-100w Med.	7½"	9¼"	4½" W, 7½" H Back Plate	
2781 OZ	3-60w Cand.			3" Dia. Post Fitter	
2782 OZ	3-60w Cand.			5½" Dia. Canopy	6', 5'
2784 OZ	2-60w Cand.	9¼"	13"	4½" W, 8¼" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

PUTNEY BRIDGE™

FINISH BLACK
GLASS CLEAR SEEDY

Putney Bridge is a classic Shaker-inspired style constructed of durable solid aluminum. The generous panels of dense seedy glass, forged metal roof and classic rivet construction combine with a bold Black finish to complete this authentic design.



2655 BK
10" W, 15¾" H



2652 BK
10" W, 17½" H



2654 BK
8" W, 13¼" H



2650 BK
6" W, 11¼" H



2651 BK
(shown as pier mount
with 1304 BK)*



2651 BK
10" W, 19¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2650 BK**	1-75w Med.	7½"	6¾"	4½" W, 9¼" H Back Plate	
2651 BK	1-100w Med.			3" Dia. Post Fitter	
2652 BK**	1-100w Med.			6" Dia. Canopy	6', 5'
2654 BK**	1-100w Med.	9½"	7¾"	4½" W, 10¾" H Back Plate	
2655 BK**	1-100w Med.	9¾"	9½"	6½" W, 12½" H Back Plate	

*Not for use within 4 ft. of ground. **When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGLIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

MONTAUK™

FINISH SIENNA
GLASS CLEAR SEEDY

The classic sophistication of the Montauk collection brings together the finest elements of traditional East Coast style. The entire collection is made from solid brass, complemented by clear seedy glass and candelabra sockets for authentic appeal.



1205 SN
1205 SN-LED
9" W, 19½" H





1202 SN
1202 SN-LED
7" W, 17¼" H
T24



1200 SN
1200 SN-LED
7" W, 17¼" H
T24



1204 SN
1204 SN-LED
7" W, 20¾" H
T24



1201 SN
1201 SN-LED
9" W, 23¾" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1200 SN	2-60w Cand.	1200 SN-LED	1-15w UNI-100	9¼"	10¼"	4½" W, 8" H Back Plate	
1201 SN	4-60w Cand.	1201 SN-LED	1-15w LESM-100			3" Dia. Post Fitter	
1202 SN	2-60w Cand.	1202 SN-LED	1-15w UNI-100			5" Dia. Canopy	6', 5'
1204 SN	3-60w Cand.	1204 SN-LED	1-15w UNI-100	9¼"	11½"	4½" W, 8" H Back Plate	
1205 SN	4-60w Cand.	1205 SN-LED	1-15w UNI-100	11¼"	10½"	4½" W, 8" H Back Plate	

For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

SEDGWICK™

FINISH SIENNA
GLASS CLEAR SEEDY

Sedgwick's brass construction symbolizes the best of vintage Hinkley quality and style. This traditional tapered rectangular lantern features a charming hinged door with sliding latch for authentic appeal. The classic Sienna finish combines beautifully with generous panels of clear seedy glass and embodies the essence of historic New England architecture and sophistication.



1775 SN
7" W, 19¾" H



1772 SN
7" W, 18¾" H



1774 SN
7" W, 19¾" H



1770 SN
4½" W, 14½" H



1771 SN
7" W, 21¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1770 SN	1-60w Cand.	6½"	9"	4½" W, 11½" H Back Plate	
1771 SN	3-60w Cand.			3" Dia. Post Fitter	
1772 SN	3-60w Cand.			5" Dia. Canopy	6', 5'
1774 SN	2-60w Cand.	6½"	14"	4½" W, 11½" H Back Plate	
1775 SN	3-60w Cand.	9½"	14"	4½" W, 11¾" H Back Plate	

For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

ANCHORAGE™

FINISH AGED ZINC
GLASS CLEAR

Anchorage is an early American lantern design crafted of solid aluminum to reflect a bold yet refined silhouette. The Aged Zinc finish and clear glass complement the long clean lines, elegant arched carriage handle and sturdy knobs, resulting in a vintage style with classic charisma.



1858 DZ
13" W, 25" H



1852 DZ
11" W, 23¾" H



1855 DZ
11" W, 21¼" H



1854 DZ
9¼" W, 17¾" H



1851 DZ
11" W, 24¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1851 DZ	3-60w Cand.			3" Dia. Post Fitter	
1852 DZ	3-60w Cand.			5¾" Dia. Canopy	6', 5'
1854 DZ	2-60w Cand.	7¾"	12¼"	4½" W, 7" H Back Plate	
1855 DZ	3-60w Cand.	9"	15½"	4½" W, 7" H Back Plate	
1858 DZ	4-60w Cand.	10¾"	17½"	4½" W, 9" H Back Plate	

For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

REVERE™

FINISH SIENNA
GLASS CLEAR SEEDY

Revere is a classic, traditional coach lantern
in solid brass with clear seedy glass panels.
The glass faux candle sleeves complete the
authentic appearance.



1185 SN
7" W, 21 $\frac{3}{4}$ " H



1182 SN
7" W, 20½" H



1184 SN
7" W, 21¾" H



1180 SN
4½" W, 17½" H



PIER MOUNT
1187 SN
6¾" W, 20¼" H



1181 SN
7" W, 22¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1180 SN	1-60w Cand.	5½"	10¼"	4½" W, 11" H Back Plate	
1181 SN	3-60w Cand.			3" Dia. Post Fitter	
1182 SN	3-60w Cand.			5" Dia. Canopy	6', 5'
1184 SN	2-60w Cand.	7¼"	12¼"	4½" W, 11" H Back Plate	
1185 SN	3-60w Cand.	10"	12¼"	4½" W, 11" H Back Plate	
1187 SN	3-60w Cand.			9¾" Square Base	

For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

BRIGHTON™

FINISH SIENNA
GLASS CLEAR SEEDY

Brighton's regal design features hand-soldered solid brass construction. The triangular-shaped stamped window pattern with circular medallion accent gives this style a distinguished sophistication.



2298 SN
2298 SN-LED
11" W, 29¼" H





ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2290 SN*	1-100w Med.	2290 SN-LED	1-15w UNI-100	7"	8"	4½" W, 11" H Back Plate	
2291 SN	3-60w Cand.	2291 SN-LED	1-15w LESM-100			3" Dia. Post Fitter	
2292 SN	3-60w Cand.	2292 SN-LED	1-10w UNI-60			5" Dia. Canopy	6', 5'
2294 SN	3-60w Cand.	2294 SN-LED	1-15w UNI-100	8¾"	10"	4½" W, 11" H Back Plate	
2295 SN	3-60w Cand.	2295 SN-LED	1-15w LESM-100	9¼"	11"	4½" W, 11" H Back Plate	
2297 SN	4-60w Cand.	2297 SN-LED	1-15w LESM-100			3" Dia. Post Fitter	
2298 SN	4-60w Cand.	2298 SN-LED	1-15w LESM-100	12"	12¼"	4½" W, 11" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky Compliant, see page 7. For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

NANTUCKET™

FINISH AGED BRASS
GLASS CLEAR SEEDY PANELS

A Hinkley classic, Nantucket features a timeless New England design for the ultimate in vintage nautical chic. An Aged Brass finish, clear seedy glass panels and durable solid brass construction add to its retro appeal.



2374 AS
7½" W, 17" H



2372 AS
5½" W, 14½" H



2370 AS
5½" W, 13½" H



2376 AS
4½" W, 9¾" H



2371 AS
7½" W, 20¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2370 AS	1-75w Med.	5½"	8¾"	5½" W, 7" H Back Plate	
2371 AS	3-60w Cand.			3" Dia. Post Fitter	
2372 AS	2-40w Cand.			5" Dia. Canopy	6', 5'
2374 AS	2-60w Cand.	6¾"	11¼"	7½" W, 8¼" H Back Plate	
2376 AS*	1-60w Med.	4½"	7"	4½" W, 5" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

BINGHAM™

FINISH SIENNA
GLASS CLEAR SEEDY

Bingham's traditional style recalls a turn-of-the-century gas light reproduction. The vintage look is nautical in nature and recognizes Hinkley's origins on the shores of Lake Erie. The brass construction features clear seedy glass and a Sienna finish, while candelabra lamping completes the authentic style.



2045 SN
8" W, 21" H



2042 SN
8" W, 23½" H



2044 SN
6" W, 16" H



2040 SN
4¾" W, 12½" H



PIER MOUNT
2047 SN
9¾" W, 21¾" H



2041 SN
8" W, 23½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2040 SN	1-60w Cand.	6½"	8"	4½" W, 7¼" H Back Plate		GS
2041 SN	3-60w Cand.			3" Dia. Post Fitter		GS
2042 SN	3-60w Cand.			5" Dia. Canopy	6', 5'	GS
2044 SN	2-60w Cand.	8"	10"	6" W, 9¼" H Back Plate		GS
2045 SN	3-60w Cand.	10¼"	13¼"	7¼" W, 12" H Back Plate		GS
2047 SN	3-60w Cand.			9¾" Square Base		GS

For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

BINGHAM™

FINISH GREYSTONE
GLASS CLEAR SEEDY

Bingham's traditional style recalls a turn-of-the-century gas light reproduction. The vintage look is nautical in nature and recognizes Hinkley's origins on the shores of Lake Erie. The aluminum construction features clear seedy glass and a Greystone finish, while candelabra lamping completes the authentic style.



2045 GS
8" W, 21" H



2042 GS
8" W, 23½" H



2044 GS
6" W, 16" H



2040 GS
4¾" W, 12½" H



PIER MOUNT
2047 GS
9¾" W, 21¾" H



2041 GS
8" W, 23½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2040 GS	1-60w Cand.	6½"	8"	4½" W, 7¼" H Back Plate		SN
2041 GS	3-60w Cand.			3" Dia. Post Fitter		SN
2042 GS	3-60w Cand.			5" Dia. Canopy	6', 5'	SN
2044 GS	2-60w Cand.	8"	10"	6" W, 9¼" H Back Plate		SN
2045 GS	3-60w Cand.	10¼"	13¼"	7¼" W, 12" H Back Plate		SN
2047 GS	3-60w Cand.			9¾" Square Base		SN

For posts and pier mounts, see pages 748-749.

Heritage
COLLECTION

PREMIUM OUTDOOR FIXTURES THAT
PAY TRIBUTE TO THE NOSTALGLIA
OF AMERICA'S PAST WHILE REINFORCING
THE HINKLEY PHILOSOPHY OF TIMELESS,
CLASSIC DESIGN.

YORK™

FINISH BLACK
GLASS CLEAR SEEDY

York uses authentic exposed rivet construction hand-made in solid aluminum and celebrates the bold traditional lantern design Hinkley is renowned for. This classic hip roof and wire cage turn of the century style comes with an optional interior metallic reflector and rolled top loop. The gallant proportions of its striking silhouette are reinforced with a vintage Black finish, cast face plate and clear seedy glass.



1845 BK
9½" W, 25" H



1842 BK
9½" W, 24¾" H



1844 BK
7½" W, 21¼" H



1840 BK
5½" W, 15¼" H



1841 BK
9½" W, 28" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1840 BK	1-100w Med.	5½"	11½"	5" Dia. Back Plate	
1841 BK	3-60w Cand.			3" Dia. Post Fitter	
1842 BK	3-60w Cand.			5" Dia. Canopy	6', 5'
1844 BK	2-60w Cand.	7½"	16"	5" Dia. Back Plate	
1845 BK	3-60w Cand.	9¼"	18¾"	5" Dia. Back Plate	

For posts and pier mounts, see pages 748-749.

TAKE THE
PARTY
OUTSIDE

LIGHTEN UP YOUR EXTERIOR WITH **ENCHANTING LANTERNS** GUARANTEED TO MAKE THE EVENING HOURS A LITTLE SWEETER. CONSIDER COPPER REFLECTORS, HINGED DOORS, GENEROUS PANELS OF GLASS AND ELEGANT CARRIAGE HANDLES AS ABUNDANT DESIGN DETAILS TO ILLUMINATE THE GREAT OUTDOORS IN STYLE.



HERITAGE. Inspiration. *Evolution.* INNOVATION.

EMBRACE THE PAST...



...LOOK TOWARD THE FUTURE

“WE ARE PROUD TO BLEND OUR HERITAGE AND INNOVATIVE SPIRIT TO PROVIDE THE MOST EXCITING, FASHION-FORWARD AND TECHNOLOGICALLY ADVANCED LIGHTING POSSIBLE.”

RIK WIEDEMER | CEO, HINKLEY LIGHTING, INC.

Hinkley has almost a century of design and manufacturing expertise in the lighting industry and that translates to a powerhouse of ingenuity. A unique combination of engineering proficiency and boundless creativity is channeled into a passion for progress: innovative lighting designs with ultra-efficient performance captured in sophisticated styles.

While honoring the past with premium lanterns crafted from archival designs and authentic construction elements, Hinkley keeps its pulse on the best trends and styles for chic outdoor lighting that blends modern technology with outstanding workmanship and the ultimate in design details.

NEWPORT™

FINISH AGED ZINC
GLASS CLEAR SEEDY

Newport is an early American classic pocket lantern featuring an optional copper reflector. Constructed in aluminum with the same quality as the traditional wharf light that served as its inspiration, the wire cage in Aged Zinc also features authentic rivet details and clear seedy glass to shield the light source.



2625 DZ
9" W, 16" H



2624 DZ
9" W, 12" H



2620 DZ
7" W, 9¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
2620 DZ	1-60w Cand.	4¼"	4¾"	4½" W, 8½" H
2624 DZ	2-60w Cand.	4¼"	6"	4¾" W, 10¼" H
2625 DZ	3-60w Cand.	4¼"	8"	4¾" W, 14½" H

SUTCLIFFE™

FINISH OIL RUBBED BRONZE
GLASS CLEAR

The Sutcliffe collection conveys chic elements of early Americana styling. The candelabra lamping, clear glass and copper reflector infuse this sleek pocket lantern design constructed of solid aluminum with a perfect blend of old and new.

OBJECT OF OUR
AFFECTION

Sleek and stylish metallic elements add warmth and "wow" to any exterior.



2915 OZ
10" W, 22" H



2914 OZ
9" W, 17" H



2910 OZ
7" W, 14" H



2911 OZ
10" W, 20" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY
2910 OZ	1-60w Cand.	5½"	8¼"	5" W, 9" H Back Plate
2911 OZ	3-60w Cand.			3" Dia. Post Fitter
2914 OZ	2-60w Cand.	5½"	9½"	5¼" W, 11½" H Back Plate
2915 OZ	3-60w Cand.	6½"	12"	7" W, 15½" H Back Plate

Ideal for vintage filament bulbs (not included). For posts and pier mounts, see pages 748-749.

BURTON™

FINISH BLACK
GLASS CLEAR BEVELED

Burton's classic cast aluminum construction in a robust Black finish is complemented by elegant touches. The distressed copper accents on the back plate, roof and socket cover paired with clear beveled glass complements the traditional styling.



1974 BK
10" W, 15¾" H



1972 BK
10" W, 18¼" H



1970 BK
8" W, 12¾" H

ITEM	BULBS	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1970 BK*	1-100w Med.	5¾"		5¼"	4½" W, 8¾" H Back Plate	
1972 BK	2-60w Cand.		6¼"		5" Dia. Canopy	6', 5'
1974 BK	2-60w Cand.	7"		5½"	4½" W, 8¾" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7.

HUDSON™

FINISH OIL RUBBED BRONZE
GLASS ETCHED OPAL

Hudson is a transitional collection with a subtle Arts & Crafts aesthetic. The clean, minimal solid aluminum metal work has a modern feel while the shallow roof lines and cast vertical posts add a refined craftsman touch.




1915 OZ
1915 OZ-GU24
1915 OZ-LED
11" W, 13½" H








1912 OZ
1912 OZ-GU24
1912 OZ-LED
11" DIA., 15½" H






1910 OZ
1910 OZ-GU24
1910 OZ-LED
7" W, 9¾" H






1914 OZ
1914 OZ-GU24
1914 OZ-LED
9" W, 12" H






1911 OZ
1911 OZ-GU24
1911 OZ-LED
11" DIA., 16¾" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1910 OZ*	1-100w Med.	1910 OZ-GU24*	1-26w GU24	1910 OZ-LED	1-15w LESM-100	8"	4¼"	4½" W, 8¼" H Back Plate	
1911 OZ	1-100w Med.	1911 OZ-GU24	1-26w GU24	1911 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
1912 OZ*	1-100w Med.	1912 OZ-GU24*	1-26w GU24	1912 OZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'
1914 OZ*	1-100w Med.	1914 OZ-GU24*	1-26w GU24	1914 OZ-LED	1-15w LESM-100	10"	4¼"	4½" W, 8¼" H Back Plate	
1915 OZ*	1-100w Med.	1915 OZ-GU24*	1-26w GU24	1915 OZ-LED	1-15w LESM-100	12"	4¼"	4½" W, 8¼" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

CHANDLER™

FINISH BLACK
GLASS ETCHED SEEDY

Chandler is a modern interpretation of the traditional gas light. A subtle nautical influence creates a transitional silhouette in die cast aluminum construction that works with a variety of exteriors.



2701 BK
2701 BK-GU24
2701 BK-LED
11" W, 20½" H
  



2700 BK
2700 BK-GU24
2700 BK-LED
8¼" W, 11½" H
  



2704 BK
2704 BK-GU24
2704 BK-LED
9" W, 14½" H
  



2705 BK
2705 BK-GU24
2705 BK-LED
11" W, 17¼" H
  

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
2700 BK*	1-100w Med.	2700 BK-GU24*	1-26w GU24	2700 BK-LED	1-15w LESM-100	9¼"	5"	5" W, 9½" H Back Plate	AR
2701 BK	1-100w Med.	2701 BK-GU24	1-26w GU24	2701 BK-LED	1-15w LESM-100			3" Dia. Post Fitter	AR
2704 BK*	1-100w Med.	2704 BK-GU24*	1-26w GU24	2704 BK-LED	1-15w LESM-100	10"	6¼"	5" W, 11½" H Back Plate	AR
2705 BK*	1-100w Med.	2705 BK-GU24*	1-26w GU24	2705 BK-LED	1-15w LESM-100	12"	7¼"	5" W, 13½" H Back Plate	AR

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Chandler is a modern interpretation of the traditional gas light. A subtle nautical influence creates a transitional silhouette in die cast aluminum construction that works with a variety of exteriors.

CHANDLER™




ANCHOR BRONZE FINISH
ETCHED SEEDY GLASS



2705 AR
2705 AR-LED
2705 AR-GU24
11" W, 17¼" H






2700 AR
2700 AR-LED
2700 AR-GU24
8¼" W, 11½" H






2704 AR
2704 AR-LED
2704 AR-GU24
9" W, 14½" H






2701 AR
2701 AR-LED
2701 AR-GU24
11" W, 20½" H





ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
2700 AR*	1-100w Med.	2700 AR-GU24*	1-26w GU24	2700 AR-LED	1-15w LESM-100	9¼"	5"	5" W, 9½" H Back Plate	BK
2701 AR	1-100w Med.	2701 AR-GU24	1-26w GU24	2701 AR-LED	1-15w LESM-100			3" Dia. Post Fitter	BK
2704 AR*	1-100w Med.	2704 AR-GU24*	1-26w GU24	2704 AR-LED	1-15w LESM-100	10"	6¼"	5" W, 11½" H Back Plate	BK
2705 AR*	1-100w Med.	2705 AR-GU24*	1-26w GU24	2705 AR-LED	1-15w LESM-100	12"	7¼"	5" W, 13½" H Back Plate	BK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

HARBOR™

FINISH TITANIUM

GLASS ETCHED SEEDY BOUND



Harbor path lights are available in the Hinkley Landscape Lighting catalog.

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the seedy glass.



2579 TT
2579 TT-GU24
2579 TT-LED
13" W, 20½" H





2572 TT
2572 TT-GU24
2572 TT-LED
11" W, 19" H
[Icons: Recycle, T24]



2575 TT
2575 TT-GU24
2575 TT-LED
11" W, 16¼" H
[Icons: Recycle, T24]



2573 TT
2573 TT-GU24
2573 TT-LED
12¼" W, 7" H
[Icons: Recycle, T24]



2570 TT
2570 TT-GU24
2570 TT-LED
7" W, 10½" H
[Icons: Recycle, T24]



2574 TT
2574 TT-GU24
2574 TT-LED
9" W, 13½" H
[Icons: Recycle, T24]



PIER MOUNT
2576 TT
2576 TT-GU24
2576 TT-LED
11" W, 17" H
[Icons: Recycle, T24]



2571 TT
2571 TT-GU24
2571 TT-LED
11" W, 19½" H
[Icons: Recycle, T24]

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2570 TT*	1-60w Med.	2570 TT-GU24*	1-13w GU24	2570 TT-LED	1-15w LESM-100	7¾"	4¾"	4½" W, 7" H Back Plate		AR, SK
2571 TT	1-100w Med.	2571 TT-GU24	1-26w GU24	2571 TT-LED	1-15w LESM-100			3" Dia. Post Fitter		AR, SK
2572 TT*	1-100w Med.	2572 TT-GU24*	1-26w GU24	2572 TT-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	AR, SK
2573 TT	2-60w Med.	2573 TT-GU24	2-13w GU24	2573 TT-LED	1-32w FSI-200					AR, SK
2574 TT*	1-75w Med.	2574 TT-GU24*	1-18w GU24	2574 TT-LED	1-15w LESM-100	10"	6"	4½" W, 9" H Back Plate		AR, SK
2575 TT*	1-100w Med.	2575 TT-GU24*	1-26w GU24	2575 TT-LED	1-15w LESM-100	11¾"	8"	4½" W, 12" H Back Plate		AR, SK
2576 TT	1-100w Med.	2576 TT-GU24	1-26w GU24	2576 TT-LED	1-15w LESM-100			8" Square Base		AR, SK
2579 TT*	1-100w Med.	2579 TT-GU24*	1-26w GU24	2579 TT-LED	1-15w LESM-100	13¼"	13¾"	4½" W, 14¼" H Back Plate		AR, SK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

HARBOR™

FINISH ANCHOR BRONZE
GLASS ETCHED SEEDY BOUND



Harbor path lights are available in the Hinkley Landscape Lighting catalog.

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the seedy glass.



2579 AR
2579 AR-GU24
2579 AR-LED
13" W, 20½" H





2572 AR
2572 AR-GU24
2572 AR-LED
11" W, 19" H









2575 AR
2575 AR-GU24
2575 AR-LED
11" W, 16¼" H










2573 AR
2573 AR-GU24
2573 AR-LED
12¼" W, 7" H




2570 AR
2570 AR-GU24
2570 AR-LED
7" W, 10½" H



2574 AR
2574 AR-GU24
2574 AR-LED
9" W, 13½" H







PIER MOUNT
2576 AR
2576 AR-GU24
2576 AR-LED
11" W, 17" H







2571 AR
2571 AR-GU24
2571 AR-LED
11" W, 19½" H






ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2570 AR*	1-60w Med.	2570 AR-GU24*	1-13w GU24	2570 AR-LED	1-15w LESM-100	7¾"	4¾"	4½" W, 7" H Back Plate		SK, TT
2571 AR	1-100w Med.	2571 AR-GU24	1-26w GU24	2571 AR-LED	1-15w LESM-100			3" Dia. Post Fitter		SK, TT
2572 AR*	1-100w Med.	2572 AR-GU24*	1-26w GU24	2572 AR-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	SK, TT
2573 AR	2-60w Med.	2573 AR-GU24	2-13w GU24	2573 AR-LED	1-32w FSI-200					SK, TT
2574 AR*	1-75w Med.	2574 AR-GU24*	1-18w GU24	2574 AR-LED	1-15w LESM-100	10"	6"	4½" W, 9" H Back Plate		SK, TT
2575 AR*	1-100w Med.	2575 AR-GU24*	1-26w GU24	2575 AR-LED	1-15w LESM-100	11¾"	8"	4½" W, 12" H Back Plate		SK, TT
2576 AR	1-100w Med.	2576 AR-GU24	1-26w GU24	2576 AR-LED	1-15w LESM-100			8" Square Base		SK, TT
2579 AR*	1-100w Med.	2579 AR-GU24*	1-26w GU24	2579 AR-LED	1-15w LESM-100	13¼"	13¾"	4½" W, 14¼" H Back Plate		SK, TT

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

HARBOR™

FINISH SATIN BLACK

GLASS ETCHED SEEDY BOUND



Harbor path lights are available in the Hinkley Landscape Lighting catalog.

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the seedy glass.



2579 SK
2579 SK-GU24
2579 SK-LED
13" W, 20½" H





2572 SK
2572 SK-GU24
2572 SK-LED
11" W, 19" H






2575 SK
2575 SK-GU24
2575 SK-LED
11" W, 16¼" H







2573 SK
2573 SK-GU24
2573 SK-LED
12¼" W, 7" H






2570 SK
2570 SK-GU24
2570 SK-LED
7" W, 10½" H






2574 SK
2574 SK-GU24
2574 SK-LED
9" W, 13½" H






PIER MOUNT
2576 SK
2576 SK-GU24
2576 SK-LED
11" W, 17" H






2571 SK
2571 SK-GU24
2571 SK-LED
11" W, 19½" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	TOP TO EXT.	OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2570 SK*	1-60w Med.	2570 SK-GU24*	1-13w GU24	2570 SK-LED	1-15w LESM-100	7¾"	4¾"	4½" W, 7" H Back Plate		AR, TT
2571 SK	1-100w Med.	2571 SK-GU24	1-26w GU24	2571 SK-LED	1-15w LESM-100			3" Dia. Post Fitter		AR, TT
2572 SK*	1-100w Med.	2572 SK-GU24*	1-26w GU24	2572 SK-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	AR, TT
2573 SK	2-60w Med.	2573 SK-GU24	2-13w GU24	2573 SK-LED	1-32w FSI-200					AR, TT
2574 SK*	1-75w Med.	2574 SK-GU24*	1-18w GU24	2574 SK-LED	1-15w LESM-100	10"	6"	4½" W, 9" H Back Plate		AR, TT
2575 SK*	1-100w Med.	2575 SK-GU24*	1-26w GU24	2575 SK-LED	1-15w LESM-100	11¾"	8"	4½" W, 12" H Back Plate		AR, TT
2576 SK	1-100w Med.	2576 SK-GU24	1-26w GU24	2576 SK-LED	1-15w LESM-100			8" Square Base		AR, TT
2579 SK*	1-100w Med.	2579 SK-GU24*	1-26w GU24	2579 SK-LED	1-15w LESM-100	13¼"	13¾"	4½" W, 14¼" H Back Plate		AR, TT

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

MANHATTAN™

FINISH OIL RUBBED BRONZE
GLASS CLEAR BEVELED

Manhattan is a classic update to the traditional train station lantern. The hand-painted Oil Rubbed Bronze finish complements the clean lines of its durable die cast construction.



2325 OZ
2325 OZ-LED
11¼" W, 18½" H





2322 OZ
2322 OZ-LED
11¼" W, 19¼" H
T24



2324 OZ
2324 OZ-LED
9¼" W, 15" H
T24



2320 OZ
2320 OZ-LED
7¼" W, 11¼" H
T24



PIER MOUNT
2327 OZ
2327 OZ-LED
11¼" W, 18½" H
T24



2321 OZ
2321 OZ-LED
11¼" W, 21½" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2320 OZ*	1-100w Med.	2320 OZ-LED	1-10w UNI-60	8"	2½"	4½" W, 5¾" H Back Plate	
2321 OZ	1-100w Med.	2321 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
2322 OZ*	1-100w Med.	2322 OZ-LED	1-15w UNI-100			5½" Square Canopy	6', 5'
2324 OZ*	1-100w Med.	2324 OZ-LED	1-15w UNI-100	10¼"	3¼"	5¼" W, 8" H Back Plate	
2325 OZ*	1-100w Med.	2325 OZ-LED	1-15w UNI-100	12½"	3¾"	7¼" W, 12" H Back Plate	
2327 OZ	1-100w Med.	2327 OZ-LED	1-15w LESM-100			9½" Square Base	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

MANHATTAN™

FINISH OIL RUBBED BRONZE
GLASS ETCHED SEEDY

Manhattan is a classic update to the traditional train station lantern. The hand-painted Oil Rubbed Bronze finish complements the clean lines of its durable die cast construction.






2235 OZ
2235 OZ-GU24
2235 OZ-LED
11¼" W, 18½" H








2232 OZ
2232 OZ-GU24
2232 OZ-LED
11¼" W, 19¼" H






2234 OZ
2234 OZ-GU24
2234 OZ-LED
9¼" W, 15" H



2230 OZ
2230 OZ-GU24
2230 OZ-LED
7¼" W, 11¾" H






PIER MOUNT
2237 OZ
2237 OZ-LED
11¼" W, 18½" H






2231 OZ
2231 OZ-GU24
2231 OZ-LED
11¼" W, 21½" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2230 OZ*	1-100w Med.	2230 OZ-GU24*	1-26w GU24	2230 OZ-LED	1-15w LESM-100	8"	2½"	4½" W, 5¾" H Back Plate	
2231 OZ	1-100w Med.	2231 OZ-GU24	1-26w GU24	2231 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
2232 OZ*	1-100w Med.	2232 OZ-GU24*	1-26w GU24	2232 OZ-LED	1-15w LESM-100			5½" Square Canopy	6', 5'
2234 OZ*	1-100w Med.	2234 OZ-GU24*	1-26w GU24	2234 OZ-LED	1-15w LESM-100	10¼"	3¼"	5¼" W, 8" H Back Plate	
2235 OZ*	1-100w Med.	2235 OZ-GU24*	1-26w GU24	2235 OZ-LED	1-15w LESM-100	12½"	3¾"	7¼" W, 12" H Back Plate	
2237 OZ	1-100w Med.	2237 OZ-GU24	1-26w GU24	2235 OZ-LED	1-15w LESM-100			9½" Square Base	




*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

COLFAX™

FINISH BRONZE
GLASS ETCHED OPAL

The sleek lines of Colfax feature intersecting planes of solid aluminum and a chic cylinder of etched opal glass to create a sophisticated geometric form. The die cast aluminum construction in a Bronze finish brings an Arts & Crafts flair to the transitional design.



2922 BZ
2922 BZ-GU24
2922 BZ-LED
9½" W, 18¾" H, 59¼" MAX. H*






2920 BZ
2920 BZ-GU24
2920 BZ-LED
6" W, 12¼" H






2924 BZ
2924 BZ-GU24
2924 BZ-LED
7½" W, 15¼" H






2925 BZ
2925 BZ-GU24
2925 BZ-LED
9½" W, 19¼" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
2920 BZ	1-100w Med.	2920 BZ-GU24	1-13w GU24	2920 BZ-LED	1-15w LESM-100	6¾"	4¼"	4½" W, 8¼" H Back Plate			PS
2922 BZ	1-100w Med.	2922 BZ-GU24	1-26w GU24	2922 BZ-LED	1-15w LESM-100			5" Dia. Canopy	10'	2-6", 2-12"	PS
2924 BZ	1-100w Med.	2924 BZ-GU24	1-18w GU24	2924 BZ-LED	1-15w LESM-100	8¼"	4¼"	4½" W, 8¼" H Back Plate			PS
2925 BZ	1-100w Med.	2925 BZ-GU24	1-26w GU24	2925 BZ-LED	1-15w LESM-100	10½"	5"	5¾" W, 10½" H Back Plate			PS




*Maximum achievable height with stems included. Additional 12" stems available, 6032 BZ. When fitted with DSL-40, Colfax fixtures are Dark Sky compliant, see page 7.

The sleek lines of Colfax feature intersecting planes of solid aluminum and a chic cylinder of etched opal glass to create a sophisticated geometric form. The stainless steel construction in a Polished Stainless Steel finish brings an Arts & Crafts flair to the transitional design.




COLFAX™

POLISHED STAINLESS STEEL FINISH
ETCHED OPAL GLASS






2925 PS
2925 PS-GU24
2925 PS-LED
9½" W, 19¼" H









2920 PS
2920 PS-GU24
2920 PS-LED
6" W, 12¼" H






2924 PS
2924 PS-GU24
2924 PS-LED
7½" W, 15¼" H






2922 PS
2922 PS-GU24
2922 PS-LED
9½" W, 18¾" H, 59¼" MAX. H*




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
2920 PS	1-100w Med.	2920 PS-GU24	1-13w GU24	2920 PS-LED	1-15w LESM-100	6¾"	4¼"	4½" W, 8¼" H Back Plate			BZ
2922 PS	1-100w Med.	2922 PS-GU24	1-26w GU24	2922 PS-LED	1-15w LESM-100			5" Dia. Canopy	10'	2-6", 2-12"	BZ
2924 PS	1-100w Med.	2924 PS-GU24	1-18w GU24	2924 PS-LED	1-15w LESM-100	8¼"	4¼"	4½" W, 8¼" H Back Plate			BZ
2925 PS	1-100w Med.	2925 PS-GU24	1-26w GU24	2925 PS-LED	1-15w LESM-100	10½"	5"	5¾" W, 10½" H Back Plate			BZ

*Maximum achievable height with stems included. Additional 12" stems available, 6032 BZ. When fitted with DSL-40, Colfax fixtures are Dark Sky compliant, see page 7.

SATURN™

FINISH SATIN BLACK
GLASS CLEAR SEEDY



Saturn path lights are available in the Hinkley Landscape Lighting catalog.

Saturn is a stunning, modern design in Satin Black, offering robust construction and intersecting lines that create a striking contrast against the clear seedy glass.



POCKET WALL MOUNT
1909 SK
8" W, 20½" H



1902 SK
10" DIA., 21¼" H



1904 SK
8" W, 16" H



POCKET WALL MOUNT
1908 SK
7¼" W, 12½" H




1900 SK
6" W, 12" H



1905 SK
10" W, 20¼" H



1901 SK
10" DIA., 21¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1900 SK	1-60w Med.	7½"	7½"	4¾" W, 9" H Back Plate		MT, SS
1901 SK	1-100w Med.			3" Dia. Post Fitter		MT, SS
1902 SK*	1-100w Med.			5" Dia. Canopy	6', 5'	MT, SS
1904 SK	1-75w Med.	9½"	9"	4¾" W, 12" H Back Plate		MT, SS
1905 SK	1-100w Med.	11½"	12¼"	4¾" W, 14" H Back Plate		MT, SS
1908 SK	2-40w Cand.	4"	6¼"	5¾" W, 12" H Back Plate		MT, SS
1909 SK	2-75w Med.	4½"	10¼"	5" W, 20" H Back Plate		MT, SS

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

SATURN™

FINISH METRO BRONZE
GLASS ETCHED OPAL



Saturn path lights are available in the Hinkley Landscape Lighting catalog.

Saturn is a stunning, modern design in Metro Bronze, offering robust construction and intersecting lines that create a striking contrast against the etched opal glass.



POCKET WALL MOUNT

1909 MT
1909 MT-GU24
1909 MT-LED
8" W, 20½" H





1902 MT
1902 MT-GU24
1902 MT-LED
10" DIA., 21¼" H










1904 MT
1904 MT-GU24
1904 MT-LED
8" W, 16" H







POCKET WALL MOUNT
1908 MT
1908 MT-GU24
1908 MT-LED
7¼" W, 12½" H






1900 MT
1900 MT-GU24
1900 MT-LED
6" W, 12" H






1905 MT
1905 MT-GU24
1905 MT-LED
10" W, 20¼" H






1901 MT
1901 MT-GU24
1901 MT-LED
10" DIA., 21¼" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1900 MT	1-60w Med.	1900 MT-GU24	1-13w GU24	1900 MT-LED	1-15w LESM-100	7½"	7½"	4¾" W, 9" H Back Plate		SK, SS
1901 MT	1-100w Med.	1901 MT-GU24	1-26w GU24	1901 MT-LED	1-15w LESM-100			3" Dia. Post Fitter		SK, SS
1902 MT*	1-100w Med.	1902 MT-GU24*	1-26w GU24	1902 MT-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	SK, SS
1904 MT	1-75w Med.	1904 MT-GU24	1-18w GU24	1904 MT-LED	1-15w LESM-100	9½"	9"	4¾" W, 12" H Back Plate		SK, SS
1905 MT	1-100w Med.	1905 MT-GU24	1-26w GU24	190 MT-LED	1-15w LESM-100	11½"	12¼"	4¾" W, 14" H Back Plate		SK, SS
1908 MT	2-40w Cand.	1908 MT-GU24	1-13w GU24	1908 MT-LED	2-8.5w LLH-60	4"	6¼"	5¾" W, 12" H Back Plate		SK, SS
1909 MT	2-75w Med.	1909 MT-GU24	2-18w GU24	1909 MT-LED	1-8.5w LLH-60 & 1-17w LLH-100	4½"	10¼"	5" W, 20" H Back Plate		SK, SS

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

SATURN™

FINISH STAINLESS STEEL
GLASS ETCHED OPAL



Saturn path lights are available in the Hinkley Landscape Lighting catalog.

Saturn is a stunning, modern design in stainless steel, offering robust construction and intersecting lines that create a striking contrast against the etched opal glass.



POCKET WALL MOUNT

1909 SS
1909 SS-GU24
1909 SS-LED
8" W, 20½" H





1902 SS
1902 SS-GU24
1902 SS-LED
10" DIA., 21¼" H











1904 SS
1904 SS-GU24
1904 SS-LED
8" W, 16" H







POCKET WALL MOUNT
1908 SS
1908 SS-GU24
1908 SS-LED
7¼" W, 12½" H



1900 SS
1900 SS-GU24
1900 SS-LED
6" W, 12" H







1905 SS
1905 SS-GU24
1905 SS-LED
10" W, 20¼" H







1901 SS
1901 SS-GU24
1901 SS-LED
10" DIA., 21¼" H





ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1900 SS	1-60w Med.	1900 SS-GU24	1-13w GU24	1900 SS-LED	1-15w LESM-100	7½"	7½"	4¾" W, 9" H Back Plate		MT, SK
1901 SS	1-100w Med.	1901 SS-GU24	1-26w GU24	1901 SS-LED	1-15w LESM-100			3" Dia. Post Fitter		MT, SK
1902 SS*	1-100w Med.	1902 SS-GU24*	1-26w GU24	1902 SS-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	MT, SK
1904 SS	1-75w Med.	1904 SS-GU24	1-18w GU24	1904 SS-LED	1-15w LESM-100	9½"	9"	4¾" W, 12" H Back Plate		MT, SK
1905 SS	1-100w Med.	1905 SS-GU24	1-26w GU24	1905 SS-LED	1-15w LESM-100	11½"	12¼"	4¾" W, 14" H Back Plate		MT, SK
1908 SS	2-40w Cand.	1908 SS-GU24	1-13w GU24	1908 SS-LED	2-8.5w LLH-60	4"	6¼"	5¾" W, 12" H Back Plate		MT, SK
1909 SS	2-75w Med.	1909 SS-GU24	2-18w GU24	1909 SS-LED	1-8.5w LLH-60 & 1-17w LLH-100	4½"	10¼"	5" W, 20" H Back Plate		MT, SK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

LUNA™

FINISH BRONZE, SATIN BLACK, SATIN WHITE, TITANIUM
GLASS ETCHED GLASS LENSES

Luna is a modern collection of solid aluminum fixtures offered in a unique combination of contemporary styles, including sleek wall lanterns with a dual light source and decorative reflector. Luna also offers chic pocket wall sconces and compact ceiling mounts that are ideal for indoor or out. Luna is standard ADA compliant.



1664 SK
1664 SK-LED
9" W, 24" H





1664 TT
1664 TT-LED
9" W, 24" H



1664 BZ
1664 BZ-LED
9" W, 24" H



1660 SK
1660 SK-LED
6" W, 16" H



1660 TT
1660 TT-LED
6" W, 16" H



1660 BZ
1660 BZ-LED
6" W, 16" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1660 BZ	2-20w MR-16*	1660 BZ-LED	2-5.5w COL-35	3½"	10" to 13½"***	6" W, 16" H
1660 SK	2-20w MR-16*	1660 SK-LED	2-5.5w COL-35	3½"	10" to 13½"***	6" W, 16" H
1660 TT	2-20w MR-16*	1660 TT-LED	2-5.5w COL-35	3½"	10" to 13½"***	6" W, 16" H
1664 BZ	2-20w MR-16*	1664 BZ-LED	2-5.5w COL-35	4"	11½" to 20½"***	9" W, 24" H
1664 SK	2-20w MR-16*	1664 SK-LED	2-5.5w COL-35	4"	11½" to 20½"***	9" W, 24" H
1664 TT	2-20w MR-16*	1664 TT-LED	2-5.5w COL-35	4"	11½" to 20½"***	9" W, 24" H

*MR-16 bulbs included. **Adjustable mounting hardware.



CEILING MOUNT
1663 BZ
 1663 BZ-GU24
 1663 BZ-LED
 8" DIA., 7¼" H



CEILING MOUNT
1663 TT
 1663 TT-GU24
 1663 TT-LED
 8" DIA., 7¼" H



CEILING MOUNT
1663 SK
 1663 SK-GU24
 1663 SK-LED
 8" DIA., 7¼" H



1647 BZ
 1647 BZ-LED
 9" W, 9" H



1647 SW
 1647 SW-LED
 9" W, 9" H



1647 SK
 1647 SK-LED
 9" W, 9" H



1647 TT
 1647 TT-LED
 9" W, 9" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1647 BZ	2-13w CFL*			1647 BZ-LED	2-5.5w COL-35	4"	4½"	4½" W, 6¾" H
1647 SK	2-13w CFL*			1647 SK-LED	2-5.5w COL-35	4"	4½"	4½" W, 6¾" H
1647 SW	2-13w CFL*			1647 SW-LED	2-5.5w COL-35	4"	4½"	4½" W, 6¾" H
1647 TT	2-13w CFL*			1647 TT-LED	2-5.5w COL-35	4"	4½"	4½" W, 6¾" H
1663 BZ	1-75w Med.	1663 BZ-GU24	1-18w GU24	1663 BZ-LED	1-15w UNI-100			
1663 SK	1-75w Med.	1663 SK-GU24	1-18w GU24	1663 SK-LED	1-15w UNI-100			
1663 TT	1-75w Med.	1663 TT-GU24	1-18w GU24	1663 TT-LED	1-15w UNI-100			

*CFL bulbs included.



1666 will cast light down



1667 will cast light up and down



POCKET DOWN LIGHT
1666 BZ
1666 BZ-GU24
1666 BZ-LED
9" W, 7" H



POCKET DOWN LIGHT
1666 TT
1666 TT-GU24
1666 TT-LED
9" W, 7" H



POCKET DOWN LIGHT
1666 SK
1666 SK-GU24
1666 SK-LED
9" W, 7" H



POCKET UP/DOWN LIGHT
1667 BZ
1667 BZ-GU24
1667 BZ-LED
9" W, 7" H



POCKET UP/DOWN LIGHT
1667 TT
1667 TT-GU24
1667 TT-LED
9" W, 7" H



POCKET UP/DOWN LIGHT
1667 SK
1667 SK-GU24
1667 SK-LED
9" W, 7" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1666 BZ	1-75w Med.	1666 BZ-GU24	1-18w GU24	1666 BZ-LED	1-5.5w COL-35	4"	3½"	9" W, 7" H
1666 SK	1-75w Med.	1666 SK-GU24	1-18w GU24	1666 SK-LED	1-5.5w COL-35	4"	3½"	9" W, 7" H
1666 TT	1-75w Med.	1666 TT-GU24	1-18w GU24	1666 TT-LED	1-5.5w COL-35	4"	3½"	9" W, 7" H
1667 BZ	1-75w Med.	1667 BZ-GU24	1-18w GU24	1667 BZ-LED	2-5.5w COL-35	4"	3½"	9" W, 7" H
1667 SK	1-75w Med.	1667 SK-GU24	1-18w GU24	1667 SK-LED	2-5.5w COL-35	4"	3½"	9" W, 7" H
1667 TT	1-75w Med.	1667 TT-GU24	1-18w GU24	1667 TT-LED	2-5.5w COL-35	4"	3½"	9" W, 7" H

ATLANTIS™

FINISH TITANIUM

GLASS CASED OPAL OR ETCHED GLASS LENSES



Atlantis path lights are available in the Hinkley Landscape Lighting catalog.


Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.

LIGHTING FOR TOMORROW
AWARD WINNER



1639 TT
1639 TT-LED
12" W, 36" H





1646 (left) will cast light down

1645 (right) will cast light up and down



1650 TT
1650 TT-GU24
1650 TT-LED
6¼" W, 10½" H



POCKET DOWN LIGHT

1646 TT
1646 TT-GU24
1646 TT-LED
9" W, 6" H



POCKET UP/DOWN LIGHT

1645 TT
1645 TT-GU24
1645 TT-LED
9" W, 6" H



1648 TT
1648 TT-LED
6" W, 16" H



1640 TT
1640 TT-LED
2¾" W, 16" H



1655 TT
1655 TT-GU24
1655 TT-LED
9" W, 15¼" H



1644 TT
1644 TT-LED
3" W, 24" H



1649 TT
1649 TT-LED
9" W, 24" H



1641 TT
1641 TT-LED
6¾" W, 23½" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT. DEPTH	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
1639 TT	3-50w GU-10*			1639 TT-LED	3-9w COL-50	4"	31"	4½" W, 6½" H	BZ, SK
1640 TT	2-20w MR-16**			1640 TT-LED	2-5.5w COL-35	6¾"	8"	4½" Square	BZ, SK
1641 TT	2-20w MR-16**			1641 TT-LED	2-5.5w COL-35		2¾"	3" Dia. Post Fitter	BZ, SK
1644 TT	2-20w MR-16**			1644 TT-LED	2-5.5w COL-35	7"	12"	4½" Square	BZ, SK
1645 TT	1-75w Med.	1645 TT-GU24	1-18w GU24	1645 TT-LED	2-5.5w COL-35	4¼"	2¾"	4½" Square	BZ, SK
1646 TT	1-75w Med.	1646 TT-GU24	1-18w GU24	1646 TT-LED	1-5.5w COL-35	4¼"	2¾"	4½" Square	BZ, SK
1648 TT	2-20w MR-16**			1648 TT-LED	2-5.5w COL-35	3½"	13¾"	4½" Square	BZ, SK
1649 TT	2-20w MR-16**			1649 TT-LED	2-5.5w COL-35	4"	20¾"	4½" W, 6½" H	BZ, SK
1650 TT	1-60w Med.	1650 TT-GU24	1-13w GU24	1650 TT-LED	1-15w LESM-100	4"	5¼"	5½" Square	BZ, SK
1655 TT	1-100w Med.	1655 TT-GU24	1-18w GU24	1655 TT-LED	1-15w LESM-100	5¾"	7¾"	5½" W, 8" H	BZ, SK

*GU-10 bulb included. **MR-16 bulbs included. For posts and pier mounts, see pages 748-749.

ATLANTIS™

FINISH BRONZE

GLASS CASED OPAL OR ETCHED GLASS LENSES



Atlantis path lights are available in the Hinkley Landscape Lighting catalog.


Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.

LIGHTING FOR TOMORROW
AWARD WINNER



1639 BZ
1639 BZ-LED
12" W, 36" H





1646 (left) will cast light down

1645 (right) will cast light up and down



1650 BZ
1650 BZ-GU24
1650 BZ-LED
6¼" W, 10½" H



POCKET DOWN LIGHT

1646 BZ
1646 BZ-GU24
1646 BZ-LED
9" W, 6" H



POCKET UP/DOWN LIGHT

1645 BZ
1645 BZ-GU24
1645 BZ-LED
9" W, 6" H



1648 BZ
1648 BZ-LED
6" W, 16" H



1640 BZ
1640 BZ-LED
2¾" W, 16" H



1655 BZ
1655 BZ-GU24
1655 BZ-LED
9" W, 15¼" H



1644 BZ
1644 BZ-LED
3" W, 24" H



1649 BZ
1649 BZ-LED
9" W, 24" H



1641 BZ
1641 BZ-LED
6¾" W, 23½" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT. DEPTH	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
1639 BZ	3-50w GU-10*			1639 BZ-LED	3-9w COL-50	4"	31"	4½" W, 6½" H	SK, TT
1640 BZ	2-20w MR-16**			1640 BZ-LED	2-5.5w COL-35	6¾"	8"	4½" Square	SK, TT
1641 BZ	2-20w MR-16**			1641 BZ-LED	2-5.5w COL-35			3" Dia. Post Fitter	SK, TT
1644 BZ	2-20w MR-16**			1644 BZ-LED	2-5.5w COL-35	7"	12"	4½" Square	SK, TT
1645 BZ	1-75w Med.	1645 BZ-GU24	1-18w GU24	1645 BZ-LED	2-5.5w COL-35	4¼"	2¾"	4½" Square	SK, TT
1646 BZ	1-75w Med.	1646 BZ-GU24	1-18w GU24	1646 BZ-LED	1-5.5w COL-35	4¼"	2¾"	4½" Square	SK, TT
1648 BZ	2-20w MR-16**			1648 BZ-LED	2-5.5w COL-35	3½"	13¾"	4½" Square	SK, TT
1649 BZ	2-20w MR-16**			1649 BZ-LED	2-5.5w COL-35	4"	20¾"	4½" W, 6½" H	SK, TT
1650 BZ	1-60w Med.	1650 BZ-GU24	1-13w GU24	1650 BZ-LED	1-15w LESM-100	4"	5¼"	5½" Square	SK, TT
1655 BZ	1-100w Med.	1655 BZ-GU24	1-18w GU24	1655 BZ-LED	1-15w LESM-100	5¾"	7¾"	5½" W, 8" H	SK, TT

*GU-10 bulb included. **MR-16 bulbs included. For posts and pier mounts, see pages 748-749.

ATLANTIS™

FINISH SATIN BLACK
GLASS ETCHED GLASS LENSES



Atlantis path lights are available in the Hinkley Landscape Lighting catalog.


Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.

LIGHTING FOR TOMORROW
AWARD WINNER



1639 SK
1639 SK-LED
12" W, 36" H





1646 (left) will cast light down

1645 (right) will cast light up and down



POCKET DOWN LIGHT

1646 SK
1646 SK-GU24
1646 SK-LED
9" W, 6" H



POCKET UP/DOWN LIGHT

1645 SK
1645 SK-GU24
1645 SK-LED
9" W, 6" H



1648 SK
1648 SK-LED
6" W, 16" H



1640 SK
1640 SK-LED
2 3/4" W, 16" H



1644 SK
1644 SK-LED
3" W, 24" H



1649 SK
1649 SK-LED
9" W, 24" H



1641 SK
1641 SK-LED
6 3/4" W, 23 1/2" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT. DEPTH	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
1639 SK	3-50w GU-10*			1639 SK-LED	3-9w COL-50	4"	31"	4 1/2" W, 6 1/2" H	BZ, TT
1640 SK	2-20w MR-16**			1640 SK-LED	2-5.5w COL-35	6 3/4"	8"	4 1/2" Square	BZ, TT
1641 SK	2-20w MR-16**			1641 SK-LED	2-5.5w COL-35		2 3/4"	3" Dia. Post Fitter	BZ, TT
1644 SK	2-20w MR-16**			1644 SK-LED	2-5.5w COL-35	7"	12"	4 1/2" Square	BZ, TT
1645 SK	1-75w Med.	1645 SK-GU24	1-18w GU24	1645 SK-LED	2-5.5w COL-35	4 1/4"	2 3/4"	4 1/2" Square	BZ, TT
1646 SK	1-75w Med.	1646 SK-GU24	1-18w GU24	1646 SK-LED	1-5.5w COL-35	4 1/4"	2 3/4"	4 1/2" Square	BZ, TT
1648 SK	2-20w MR-16**			1648 SK-LED	2-5.5w COL-35	3 1/2"	13 3/4"	4 1/2" Square	BZ, TT
1649 SK	2-20w MR-16**			1649 SK-LED	2-5.5w COL-35	4"	20 3/4"	4 1/2" W, 6 1/2" H	BZ, TT

*GU-10 bulb included. **MR-16 bulbs included. For posts and pier mounts, see pages 748-749.

TITAN™

FINISH BUCKEYE BRONZE, HEMATITE, TITANIUM
GLASS ORGANIC RIBBED ETCHED

Titan's sleek design in solid aluminum features organic etched glass that creates an indirect wall wash for a sophisticated appearance.



2054 HE
2054 HE-GU24
8½" W, 17½" H





2054 KZ
2054 KZ-GU24
8½" W, 17½" H



2054 TT
2054 TT-GU24
8½" W, 17½" H



2050 HE
2050 HE-GU24
6¾" W, 14" H



2050 KZ
2050 KZ-GU24
6¾" W, 14" H



2050 TT
2050 TT-GU24
6¾" W, 14" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	EXT.	TOP TO OUTLET	BACK PLATE
2050 HE	1-100w Med.	2050 HE-GU24	1-26w GU24	4½"	7"	6¾" W, 14" H
2050 KZ	1-100w Med.	2050 KZ-GU24	1-26w GU24	4½"	7"	6¾" W, 14" H
2050 TT	1-100w Med.	2050 TT-GU24	1-26w GU24	4½"	7"	6¾" W, 14" H
2054 HE	1-100w Med.	2054 HE-GU24	1-26w GU24	4¾"	8¾"	8½" W, 17½" H
2054 KZ	1-100w Med.	2054 KZ-GU24	1-26w GU24	4¾"	8¾"	8½" W, 17½" H
2054 TT	1-100w Med.	2054 TT-GU24	1-26w GU24	4¾"	8¾"	8½" W, 17½" H

DISTRICT™

FINISH BRONZE, TITANIUM
GLASS ETCHED RAIN

District is a contemporary design of solid aluminum construction with a sleek panel of 1/4" bent rain glass on the front of the lantern. Available in two finishes, the angled side panels in this collection feature vents of etched glass, adding a soft yet modern design element.



2115 BZ
2115 BZ-GU24
2115 BZ-LED
7¼" W, 24" H
🔄 ⚡ 124



2115 TT
2115 TT-GU24
2115 TT-LED
7¼" W, 24" H
🔄 ⚡ 124






Angled side and bottom view
of glass panels on 2110 TT



2110 BZ
2110 BZ-GU24
2110 BZ-LED
7¼" W, 12" H
  



2110 TT
2110 TT-GU24
2110 TT-LED
7¼" W, 12" H
  



2114 BZ
2114 BZ-GU24
2114 BZ-LED
7¼" W, 18" H
  



2114 TT
2114 TT-GU24
2114 TT-LED
7¼" W, 18" H
  

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
2110 BZ	1-100w Med.	2110 BZ-GU24	1-26w GU24	2110 BZ-LED	1-15w LESM-100	4½"	6"	4½" W, 6¾" H
2110 TT	1-100w Med.	2110 TT-GU24	1-26w GU24	2110 TT-LED	1-15w LESM-100	4½"	6"	4½" W, 6¾" H
2114 BZ	1-100w Med.	2114 BZ-GU24	1-26w GU24	2114 BZ-LED	1-15w LESM-100	4½"	9"	4½" W, 6¾" H
2114 TT	1-100w Med.	2114 TT-GU24	1-26w GU24	2114 TT-LED	1-15w LESM-100	4½"	9"	4½" W, 6¾" H
2115 BZ	2-100w Med.	2115 BZ-GU24	2-26w GU24	2115 BZ-LED	2-15w LESM-100	4½"	12"	4½" W, 6¾" H
2115 TT	2-100w Med.	2115 TT-GU24	2-26w GU24	2115 TT-LED	2-15w LESM-100	4½"	12"	4½" W, 6¾" H

CASCADE™

FINISH BRONZE, SATIN BLACK, TITANIUM
 GLASS CLEAR ETCHED ORGANIC RAIN,
 AMBER ETCHED ORGANIC RAIN

The clean, modern lines of Cascade complement the rain glass while creating a glowing, indirect lighting effect. The sleek aluminum construction adds to the design's versatility, making this contemporary style perfect for either interior or exterior use. Cascade is standard Dark Sky compliant.



1830 BZ
 1830 BZ-GU24
 1830 BZ-LED
 8" W, 14½" H

Icons: [Dark Sky], [Rain Glass], [Moon], [T24], [ADA]



1830 TT
 1830 TT-GU24
 1830 TT-LED
 8" W, 14½" H

Icons: [Dark Sky], [Rain Glass], [Moon], [T24], [ADA]



1830 SK
 1830 SK-GU24
 1830 SK-LED
 8" W, 14½" H

Icons: [Dark Sky], [Rain Glass], [Moon], [T24], [ADA]



1834 BZ
 1834 BZ-GU24
 1834 BZ-LED
 8" W, 18" H

Icons: [Dark Sky], [Rain Glass], [Moon], [T24], [ADA]



1834 TT
 1834 TT-GU24
 1834 TT-LED
 8" W, 18" H

Icons: [Dark Sky], [Rain Glass], [Moon], [T24], [ADA]



1834 SK
 1834 SK-GU24
 1834 SK-LED
 8" W, 18" H

Icons: [Dark Sky], [Rain Glass], [Moon], [T24], [ADA]



side view of 1831 BZ



side view of 1831 TT




side view of 1831 SK



1831 BZ
1831 BZ-GU24
1831 BZ-LED
9½" W, 22½" H




1831 TT
1831 TT-GU24
1831 TT-LED
9½" W, 22½" H




1831 SK
1831 SK-GU24
1831 SK-LED
9½" W, 22½" H


ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1830 BZ	1-100w Med.	1830 BZ-GU24	1-26w GU24	1830 BZ-LED	1-15w UNI-100	4"	4¾"	8" W, 14½" H
1830 SK	1-100w Med.	1830 SK-GU24	1-26w GU24	1830 SK-LED	1-15w UNI-100	4"	4¾"	8" W, 14½" H
1830 TT	1-100w Med.	1830 TT-GU24	1-26w GU24	1830 TT-LED	1-15w UNI-100	4"	4¾"	8" W, 14½" H
1831 BZ	1-100w Med.	1831 BZ-GU24	1-26w GU24	1831 BZ-LED	1-15w UNI-100			3" Dia. Post Fitter
1831 SK	1-100w Med.	1831 SK-GU24	1-26w GU24	1831 SK-LED	1-15w UNI-100			3" Dia. Post Fitter
1831 TT	1-100w Med.	1831 TT-GU24	1-26w GU24	1831 TT-LED	1-15w UNI-100			3" Dia. Post Fitter
1834 BZ	1-100w Med.	1834 BZ-GU24	1-26w GU24	1834 BZ-LED	1-15w UNI-100	4"	4¾"	8" W, 18" H
1834 SK	1-100w Med.	1834 SK-GU24	1-26w GU24	1834 SK-LED	1-15w UNI-100	4"	4¾"	8" W, 18" H
1834 TT	1-100w Med.	1834 TT-GU24	1-26w GU24	1834 TT-LED	1-15w UNI-100	4"	4¾"	8" W, 18" H

For posts and pier mounts, see pages 748-749.

KUBE™

FINISH BRONZE, SATIN BLACK, TITANIUM

GLASS CLEAR ETCHED ORGANIC RAIN,
AMBER ETCHED ORGANIC RAIN, ETCHED LENSES

A collection of sleek designs, Kube's contemporary style featuring solid aluminum construction provides a chic, minimalist statement to complement a variety of exteriors. Kube is standard Dark Sky compliant.



1760 SK
1760 SK-LED
4½" W, 12" H
☀️ 🌙 T24



1760 TT
1760 TT-LED
4½" W, 12" H
☀️ 🌙 T24



1760 BZ
1760 BZ-LED
4½" W, 12" H
☀️ 🌙 T24



1764 SK
1764 SK-LED
6" W, 16" H
☀️ 🌙 T24



1764 TT
1764 TT-LED
6" W, 16" H
☀️ 🌙 T24



1764 BZ
1764 BZ-LED
6" W, 16" H
☀️ 🌙 T24



CEILING MOUNT
1763 BZ
1763 BZ-GU24
1763 BZ-LED
6" W, 6¼" H



CEILING MOUNT
1763 TT
1763 TT-GU24
1763 TT-LED
6" W, 6¼" H



CEILING MOUNT
1763 SK
1763 SK-GU24
1763 SK-LED
6" W, 6¼" H



1761 BZ
1761 BZ-GU24
1761 BZ-LED
6" W, 18½" H



1761 TT
1761 TT-GU24
1761 TT-LED
6" W, 18½" H



1761 SK
1761 SK-GU24
1761 SK-LED
6" W, 18½" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1760 BZ	1-50w GU-10*			1760 BZ-LED	1-10w UNI-60	5"	5½"	4½" W, 6¾" H
1760 SK	1-50w GU-10*			1760 SK-LED	1-10w UNI-60	5"	5½"	4½" W, 6¾" H
1760 TT	1-50w GU-10*			1760 TT-LED	1-10w UNI-60	5"	5½"	4½" W, 6¾" H
1761 BZ	2-50w GU-10*			1761 BZ-LED	1-15w UNI-100			3" Dia. Post Fitter
1761 SK	2-50w GU-10*			1761 SK-LED	1-15w UNI-100			3" Dia. Post Fitter
1761 TT	2-50w GU-10*			1761 TT-LED	1-15w UNI-100			3" Dia. Post Fitter
1763 BZ	1-75w Med.	1763 BZ-GU24	1-18w GU24	1763 BZ-LED	1-15w UNI-100			
1763 SK	1-75w Med.	1763 SK-GU24	1-18w GU24	1763 SK-LED	1-15w UNI-100			
1763 TT	1-75w Med.	1763 TT-GU24	1-18w GU24	1763 TT-LED	1-15w UNI-100			
1764 BZ	1-50w GU-10*			1764 BZ-LED	1-10w UNI-60	6½"	8"	4½" W, 6¾" H
1764 SK	1-50w GU-10*			1764 SK-LED	1-10w UNI-60	6½"	8"	4½" W, 6¾" H
1764 TT	1-50w GU-10*			1764 TT-LED	1-10w UNI-60	6½"	8"	4½" W, 6¾" H

*GU-10 bulb included. For posts and pier mounts, see pages 748-749.



1766 will cast light down



1767 will cast light up and down



POCKET DOWN LIGHT
1766 BZ
1766 BZ-GU24
1766 BZ-LED
6" W, 6" H



POCKET DOWN LIGHT
1766 TT
1766 TT-GU24
1766 TT-LED
6" W, 6" H



POCKET DOWN LIGHT
1766 SK
1766 SK-GU24
1766 SK-LED
6" W, 6" H



POCKET UP/DOWN LIGHT
1767 BZ
1767 BZ-GU24
1767 BZ-LED
6" W, 6" H



POCKET UP/DOWN LIGHT
1767 TT
1767 TT-GU24
1767 TT-LED
6" W, 6" H



POCKET UP/DOWN LIGHT
1767 SK
1767 SK-GU24
1767 SK-LED
6" W, 6" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1766 BZ	1-75w Med.	1766 BZ-GU24	1-18w GU24	1766 BZ-LED	1-5.5w COL-35	6¾"	3"	4½" Square
1766 SK	1-75w Med.	1766 SK-GU24	1-18w GU24	1766 SK-LED	1-5.5w COL-35	6¾"	3"	4½" Square
1766 TT	1-75w Med.	1766 TT-GU24	1-18w GU24	1766 TT-LED	1-5.5w COL-35	6¾"	3"	4½" Square
1767 BZ	1-75w Med.	1767 BZ-GU24	1-18w GU24	1767 BZ-LED	2-5.5w COL-35	6¾"	3"	4½" Square
1767 SK	1-75w Med.	1767 SK-GU24	1-18w GU24	1767 SK-LED	2-5.5w COL-35	6¾"	3"	4½" Square
1767 TT	1-75w Med.	1767 TT-GU24	1-18w GU24	1767 TT-LED	2-5.5w COL-35	6¾"	3"	4½" Square

Lex is a lantern formed out of geometric shapes that embodies modern design. Architectural in look and feel, Lex offers a striking silhouette in durable aluminum and solid stainless steel construction combined with LED technology for a bold contemporary statement.

LEX™

BRONZE, STAINLESS STEEL FINISH



2715 SS
10½" W, 22" H
T24

2715 BZ
10½" W, 22" H
T24

2714 SS
8½" W, 15" H
T24

2714 BZ
8½" W, 15" H
T24

ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
2714 BZ	1-15w UNI-100	5"	7½"	4½" W, 6¾" H
2714 SS	1-15w UNI-100	5"	7½"	4½" W, 6¾" H
2715 BZ	1-15w UNI-100	5½"	11"	4½" W, 6¾" H
2715 SS	1-15w UNI-100	5½"	11"	4½" W, 6¾" H

VENTO™

FINISH BRONZE

Vento's versatile design in a Bronze finish and solid aluminum construction features a series of crisp triangular forms complemented by a stunning interior reflective plate of hammered copper for modern style with vintage flair. Vento comes standard Dark Sky Compliant.



2180 BZ
2180 BZ-LED
6" W, 9" H



2185 BZ
2185 BZ-LED
8" W, 18" H



2184 BZ
2184 BZ-LED
8" W, 12" H



ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2180 BZ	1-50w GU-10*	2180 BZ-LED	1-5w DSLG-40	4"	4"	4¾" Square	SK
2184 BZ	1-50w GU-10*	2184 BZ-LED	1-5w DSLG-40	5"	5"	4¾" Square	SK
2185 BZ	1-50w GU-10*	2185 BZ-LED	1-5w DSLG-40	5½"	9"	4¾" Square	SK

*GU-10 bulb included.

Vento's versatile design in a Satin Black finish and solid aluminum construction features a series of crisp triangular forms complemented by a stunning interior reflective plate of brushed nickel for modern style with vintage flair. Vento comes standard Dark Sky Compliant.

VENTO™

SATIN BLACK FINISH



2184 SK
2184 SK-LED
8" W, 12" H



2185 SK
2185 SK-LED
8" W, 18" H



2180 SK
2180 SK-LED
6" W, 9" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2180 SK	1-50w GU-10*	2180 SK-LED	1-5w DSLG-40	4"	4"	4¾" Square	BZ
2184 SK	1-50w GU-10*	2184 SK-LED	1-5w DSLG-40	5"	5"	4¾" Square	BZ
2185 SK	1-50w GU-10*	2185 SK-LED	1-5w DSLG-40	5½"	9"	4¾" Square	BZ

*GU-10 bulb included.

SURF™



FINISH BRONZE, STAINLESS STEEL

Surf's chic design reflects the natural curl of a breaking wave. Constructed of solid stainless steel as well as solid aluminum, this LED lantern emits light both up and down.



2355 BZ
9½" W, 24" H
 



2355 SS
9½" W, 24" H
 



2350 BZ
6" W, 15" H
T24



2350 SS
6" W, 15" H
T24



2354 BZ
7½" W, 19" H
T24



2354 SS
7½" W, 19" H
T24

ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
2350 BZ	2-10w UNI-60	4¾"	8¾"	4½" W, 7½" H
2350 SS	2-10w UNI-60	4¾"	8¾"	4½" W, 7½" H
2354 BZ	2-13w UNI-75	5¾"	11"	4½" W, 7½" H
2354 SS	2-13w UNI-75	5¾"	11"	4½" W, 7½" H
2355 BZ	2-15w UNI-100	7"	13¾"	4½" W, 11½" H
2355 SS	2-15w UNI-100	7"	13¾"	4½" W, 11½" H

ARIA™

FINISH BUCKEYE BRONZE

Aria is a contemporary style that effortlessly complements the façade of any exterior. Its modern shape in durable aluminum is enhanced by a stainless steel mesh shade. Aria comes standard Dark Sky compliant.



2305 KZ
2305 KZ-GU24
2305 KZ-LED
7" W, 21³/₄" H





2302 KZ
2302 KZ-GU24
2302 KZ-LED
5" W, 19¼" H
5½" MAX. H*



2300 KZ
2300 KZ-GU24
2300 KZ-LED
5" W, 15½" H



2306 KZ
2306 KZ-GU24
2306 KZ-LED
4½" W, 14½" H



2304 KZ
2304 KZ-GU24
2304 KZ-LED
5" W, 18½" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2300 KZ	1-75w Med.	2300 KZ-GU24	1-18w GU24	2300 KZ-LED	1-5w DSLG-40	6¾"	5"	4½" W, 8¼" H Back Plate		
2302 KZ	1-100w Med.	2302 KZ-GU24	1-26w GU24	2302 KZ-LED	1-5w DSLG-40			6" Dia. Canopy	10'	1-6", 2-12"
2304 KZ	1-100w Med.	2304 KZ-GU24	1-26w GU24	2304 KZ-LED	1-5w DSLG-40	6¾"	5"	4½" W, 8¼" H Back Plate		
2305 KZ	1-100w Med.	2305 KZ-GU24	1-26w GU24	2305 KZ-LED	1-5w DSLG-40	8¾"	5"	4½" W, 8¼" H Back Plate		
2306 KZ	1-60w Med.	2306 KZ-GU24	1-13w GU24	2306 KZ-LED	1-5w DSLG-40	4¾"	5"	4½" W, 8¼" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 4312 KZ. Reflector type or Par type lamp recommended.

SHELTER™

FINISH BLACK
GLASS CLEAR SEEDY



Shelter path lights are available in the Hinkley Landscape Lighting catalog.

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.



1325 BK
1325 BK-GU24
1325 BK-LED
8¼" W, 23¼" H





1328 BK
1328 BK-GU24
1328 BK-LED
8¼" DIA., 24½" H
57" MAX. H*



1322 BK
1322 BK-GU24
1322 BK-LED
6¼" DIA., 21¾" H
54" MAX. H*



1326 BK
1326 BK-GU24
1326 BK-LED
4½" W, 15½" H



1324 BK
1324 BK-GU24
1324 BK-LED
6¼" W, 20½" H



1320 BK
1320 BK-GU24
1320 BK-LED
6¼" W, 15½" H



1321 BK
1321 BK-GU24
1321 BK-LED
(shown as pier mount
with 1304 BK)**
8¼" DIA., 27¾" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
1320 BK	1-75w Med.	1320 BK-GU24	1-13w GU24	1320 BK-LED	1-10w UNI-60	6½"	5¾"	4½" W, 12" H Back Plate			HE, KZ
1321 BK	1-100w Med.	1321 BK-GU24	1-18w GU24	1321 BK-LED	1-15w UNI-100			3" Dia. Post Fitter			HE, KZ
1322 BK	1-100w Med.	1322 BK-GU24	1-26w GU24	1322 BK-LED	1-15w UNI-100			6" Dia. Canopy	10'	1-6", 2-12"	HE, KZ
1324 BK	1-100w Med.	1324 BK-GU24	1-18w GU24	1324 BK-LED	1-15w UNI-100	6½"	5¾"	4½" W, 12" H Back Plate			HE, KZ
1325 BK	1-100w Med.	1325 BK-GU24	1-18w GU24	1325 BK-LED	1-15w UNI-100	8½"	5¾"	4½" W, 12" H Back Plate			HE, KZ
1326 BK	1-60w Med.	1326 BK-GU24	1-13w GU24	1326 BK-LED	1-5w DSLG-40	4¾"	5¾"	4½" W, 12" H Back Plate			HE, KZ
1328 BK	1-100w Med.	1328 BK-GU24	1-26w GU24	1328 BK-LED	1-15w UNI-100			6" Dia. Canopy	10'	1-6", 2-12"	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BK. **Not for use within 4 ft. of ground. Reflector type or Par type lamp recommended. For posts and pier mounts, see pages 748-749.

SHELTER™

FINISH HEMATITE
GLASS CLEAR SEEDY



Shelter path lights are available in the Hinkley Landscape Lighting catalog.

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.



1325 HE
1325 HE-GU24
1325 HE-LED
8¼" W, 23¼" H





1322 HE
1322 HE-GU24
1322 HE-LED
6¼" DIA., 21¾" H
54" MAX. H*



1326 HE
1326 HE-GU24
1326 HE-LED
4½" W, 15½" H



1320 HE
1320 HE-GU24
1320 HE-LED
6¼" W, 15½" H



1324 HE
1324 HE-GU24
1324 HE-LED
6¼" W, 20½" H



1321 HE
1321 HE-GU24
1321 HE-LED
8¼" DIA., 27¾" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	STEMS INCLUDED	ADDITIONAL FINISHES
1320 HE	1-75w Med.	1320 HE-GU24	1-13w GU24	1320 HE-LED	1-10w UNI-60	6½"	5¾"	4½" W, 12" H Back Plate		BK, KZ
1321 HE	1-100w Med.	1321 HE-GU24	1-18w GU24	1321 HE-LED	1-15w UNI-100			3" Dia. Post Fitter		BK, KZ
1322 HE	1-100w Med.	1322 HE-GU24	1-26w GU24	1322 HE-LED	1-15w UNI-100			6" Dia. Canopy	10'	1-6", 2-12"
1324 HE	1-100w Med.	1324 HE-GU24	1-18w GU24	1324 HE-LED	1-15w UNI-100	6½"	5¾"	4½" W, 12" H Back Plate		BK, KZ
1325 HE	1-100w Med.	1325 HE-GU24	1-18w GU24	1325 HE-LED	1-15w UNI-100	8½"	5¾"	4½" W, 12" H Back Plate		BK, KZ
1326 HE	1-60w Med.	1326 HE-GU24	1-13w GU24	1326 HE-LED	1-5w DSLG-40	4¾"	5¾"	4½" W, 12" H Back Plate		BK, KZ

*Maximum achievable height with stems included. Additional 12" stems available, 4312 HE. Reflector type or Par type lamp recommended. For posts and pier mounts, see pages 748-749.

SHELTER™

FINISH BUCKEYE BRONZE
GLASS CLEAR SEEDY



Shelter path lights are available in the Hinkley Landscape Lighting catalog.

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.



1325 KZ
1325 KZ-GU24
1325 KZ-LED
8¼" W, 23¼" H





1322 KZ
1322 KZ-GU24
1322 KZ-LED
6¼" DIA., 21¾" H
54" MAX. H*
☞ ☻ ☾ T24



1326 KZ
1326 KZ-GU24
1326 KZ-LED
4½" W, 15½" H
☞ ☻ ☾



1320 KZ
1320 KZ-GU24
1320 KZ-LED
6¼" W, 15½" H
☞ ☻ ☾ T24



1324 KZ
1324 KZ-GU24
1324 KZ-LED
6¼" W, 20½" H
☞ ☻ ☾ T24



1321 KZ
1321 KZ-GU24
1321 KZ-LED
8¼" DIA., 27¾" H
☞ ☻ ☾ T24

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	STEMS INCLUDED	ADDITIONAL FINISHES
1320 KZ	1-75w Med.	1320 KZ-GU24	1-13w GU24	1320 KZ-LED	1-10w UNI-60	6½"	5¾"	4½" W, 12" H Back Plate		BK, HE
1321 KZ	1-100w Med.	1321 KZ-GU24	1-18w GU24	1321 KZ-LED	1-15w UNI-100			3" Dia. Post Fitter		BK, HE
1322 KZ	1-100w Med.	1322 KZ-GU24	1-26w GU24	1322 KZ-LED	1-15w UNI-100			6" Dia. Canopy	10'	1-6", 2-12" BK, HE
1324 KZ	1-100w Med.	1324 KZ-GU24	1-18w GU24	1324 KZ-LED	1-15w UNI-100	6½"	5¾"	4½" W, 12" H Back Plate		BK, HE
1325 KZ	1-100w Med.	1325 KZ-GU24	1-18w GU24	1325 KZ-LED	1-15w UNI-100	8½"	5¾"	4½" W, 12" H Back Plate		BK, HE
1326 KZ	1-60w Med.	1326 KZ-GU24	1-13w GU24	1326 KZ-LED	1-5w DSLG-40	4¾"	5¾"	4½" W, 12" H Back Plate		BK, HE

*Maximum achievable height with stems included. Additional 12" stems available, 4312 KZ. Reflector type or Par type lamp recommended. For posts and pier mounts, see pages 748-749.

SOLO™


FINISH BRONZE
GLASS ETCHED OPAL

The Solo collection is a minimal yet striking design constructed from thick, solid aluminum. Distinctive diagonal elements are repeated throughout the fixture and glass cylinder to create a visual zigzag, adding a bold design element.



2065 BZ
2065 BZ-GU24
2065 BZ-LED
8" W, 20¾" H




2064 BZ
2064 BZ-GU24
2064 BZ-LED
7" W, 16¾" H




2060 BZ
2060 BZ-GU24
2060 BZ-LED
6" W, 14" H


ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2060 BZ	1-100w Med.	2060 BZ-GU24	1-18w GU24	2060 BZ-LED	1-15w LESM-100	7½"	3¾"	4¾" Square	SK
2064 BZ	1-100w Med.	2064 BZ-GU24	1-26w GU24	2064 BZ-LED	1-15w LESM-100	8½"	4½"	4¾" Square	SK
2065 BZ	1-100w Med.	2065 BZ-GU24	1-26w GU24	2065 BZ-LED	1-15w LESM-100	9½"	5"	4¾" Square	SK

When fitted with DSL-40, Solo fixtures are Dark Sky compliant, see page 7.

The Solo collection is a minimal yet striking design constructed from thick, solid aluminum. Distinctive diagonal elements are repeated throughout the fixture and glass cylinder to create a visual zigzag, adding a bold design element.

SOLO™

SATIN BLACK FINISH
ETCHED OPAL GLASS

THE SUGGESTION BOX Choose your glass position for a customized look.



2065 SK
2065 SK-GU24
2065 SK-LED
8" W, 20¾" H
[Icons: DALI, GU24, T24]



2064 SK
2064 SK-GU24
2064 SK-LED
7" W, 16¾" H
[Icons: DALI, GU24, T24]



2060 SK
2060 SK-GU24
2060 SK-LED
6" W, 14" H
[Icons: DALI, GU24, T24]

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2060 SK	1-100w Med.	2060 SK-GU24	1-18w GU24	2060 SK-LED	1-15w LESM-100	7½"	3¾"	4¾" Square	BZ
2064 SK	1-100w Med.	2064 SK-GU24	1-26w GU24	2064 SK-LED	1-15w LESM-100	8½"	4½"	4¾" Square	BZ
2065 SK	1-100w Med.	2065 SK-GU24	1-26w GU24	2065 SK-LED	1-15w LESM-100	9½"	5"	4¾" Square	BZ

When fitted with DSL-40, Solo fixtures are Dark Sky compliant, see page 7.

SOLARA™

FINISH BRONZE
GLASS INSIDE WHITE ETCHED

Solara offers a chic, modern style with solid aluminum construction in a wall pocket mounting. The bottom lens provides optimal down lighting.



2026 BZ
2026 BZ-GU24
2026 BZ-LED
6" W, 14" H



2020 BZ
2020 BZ-GU24
2020 BZ-LED
9" W, 9" H



side view of 2021 BZ



2024 BZ
2024 BZ-GU24
2024 BZ-LED
9" W, 15½" H



2025 BZ
2025 BZ-GU24
2025 BZ-LED
9" W, 22" H



2021 BZ
2021 BZ-GU24
2021 BZ-LED
8" W, 20½" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	ADDITIONAL FINISHES
2020 BZ	1-100w Med.	2020 BZ-GU24	1-18w GU24	2020 BZ-LED	1-15w LESM-100	4"	3¼"	9" Square Back Plate	TT
2021 BZ	1-100w Med.	2021 BZ-GU24	1-18w GU24	2021 BZ-LED	1-15w LESM-100			3" Dia. Post Fitter	TT
2024 BZ	1-100w Med.	2024 BZ-GU24	1-18w GU24	2024 BZ-LED	1-15w LESM-100	4"	4"	9" W, 15½" Back Plate	TT
2025 BZ	2-100w Med.	2025 BZ-GU24	2-18w GU24	2025 BZ-LED	2-15w LESM-100	4"	11"	9" W, 22" H Back Plate	TT
2026 BZ	1-100w Med.	2026 BZ-GU24	1-18w GU24	2026 BZ-LED	1-15w LESM-100	3½"	6"	6" W, 14" H Back Plate	TT

For posts and pier mounts, see pages 748-749.

Solara offers a chic, modern style with solid aluminum construction in a wall pocket mounting. The bottom lens provides optimal down lighting.

SOLARA™

TITANIUM FINISH
INSIDE WHITE ETCHED GLASS



side view of 2021 TT



2020 TT
2020 TT-GU24
2020 TT-LED
9" W, 9" H



2026 TT
2026 TT-GU24
2026 TT-LED
6" W, 14" H



2021 TT
2021 TT-GU24
2021 TT-LED
8" W, 20½" H



2025 TT
2025 TT-GU24
2025 TT-LED
9" W, 22" H



2024 TT
2024 TT-GU24
2024 TT-LED
9" W, 15½" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	ADDITIONAL FINISHES
2020 TT	1-100w Med.	2020 TT-GU24	1-18w GU24	2020 TT-LED	1-15w LESM-100	4"	3¼"	9" Square Back Plate	BZ
2021 TT	1-100w Med.	2021 TT-GU24	1-18w GU24	2021 TT-LED	1-15w LESM-100			3" Dia. Post Fitter	BZ
2024 TT	1-100w Med.	2024 TT-GU24	1-18w GU24	2024 TT-LED	1-15w LESM-100	4"	4"	9" W, 15½" Back Plate	BZ
2025 TT	2-100w Med.	2025 TT-GU24	2-18w GU24	2025 TT-LED	2-15w LESM-100	4"	11"	9" W, 22" H Back Plate	BZ
2026 TT	1-100w Med.	2026 TT-GU24	1-18w GU24	2026 TT-LED	1-15w LESM-100	3½"	6"	6" W, 14" H Back Plate	BZ

For posts and pier mounts, see pages 748-749.

DORIAN™

FINISH TITANIUM
GLASS CLEAR PAINTED WHITE INSIDE

Dorian's robust design in durable aluminum construction is offered in either Titanium or Bronze finishes. This contemporary fixture allows light to emit from white etched glass windows on five sides.



2190 TT
2190 TT-GU24
2190 TT-LED
6" W, 12½" H



2191 TT
2191 TT-GU24
2191 TT-LED
6" W, 20¾" H



2194 TT
2194 TT-GU24
2194 TT-LED
6" W, 18¼" H



2195 TT
2195 TT-GU24
2195 TT-LED
6" W, 25¼" H



2192 TT
2192 TT-GU24
2192 TT-LED
6" W, 18¼" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	ADDITIONAL FINISHES
2190 TT	1-100w Med.	2190 TT-GU24	1-18w GU24	2190 TT-LED	2-8.5w LLH-60	6¾"	6¼"	4½" Square Back Plate		BZ
2191 TT	1-100w Med.	2191 TT-GU24	1-18w GU24	2191 TT-LED	1-15w LESM-100			3" Dia. Post Fitter		BZ
2192 TT	1-100w Med.	2192 TT-GU24	1-18w GU24	2192 TT-LED	1-15w LESM-100			5" Dia. Canopy	6'	BZ
2194 TT	2-100w Med.	2194 TT-GU24	1-18w GU24	2194 TT-LED	1-17w LLH-100	6¾"	9¼"	4½" Square Back Plate		BZ
2195 TT	2-100w Med.	2195 TT-GU24	2-18w GU24	2195 TT-LED	1-17w LLH-100 & 1-8.5w LLH-60	6¾"	12½"	4½" Square Back Plate		BZ

For posts and pier mounts, see pages 748-749.

Dorian's robust design in durable aluminum construction is offered in either Titanium or Bronze finishes. This contemporary fixture allows light to emit from white etched glass windows on five sides.

DORIAN™

BRONZE FINISH
CLEAR PAINTED WHITE INSIDE GLASS



2192 BZ
2192 BZ-GU24
2192 BZ-LED
6" W, 18¼" H
[Icons: Recycle, T24]



2195 BZ
2195 BZ-GU24
2195 BZ-LED
6" W, 25¼" H
[Icons: Recycle]



2190 BZ
2190 BZ-GU24
2190 BZ-LED
6" W, 12½" H
[Icons: Recycle, T24]



2194 BZ
2194 BZ-GU24
2194 BZ-LED
6" W, 18¼" H
[Icons: Recycle]



2191 BZ
2191 BZ-GU24
2191 BZ-LED
6" W, 20¾" H
[Icons: Recycle, T24]

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	ADDITIONAL FINISHES
2190 BZ	1-100w Med.	2190 BZ-GU24	1-18w GU24	2190 BZ-LED	2-8.5w LLH-60	6¾"	6¼"	4½" Square Back Plate		TT
2191 BZ	1-100w Med.	2191 BZ-GU24	1-18w GU24	2191 BZ-LED	1-15w LESM-100			3" Dia. Post Fitter		TT
2192 BZ	1-100w Med.	2192 BZ-GU24	1-18w GU24	2192 BZ-LED	1-15w LESM-100			5" Dia. Canopy	6'	TT
2194 BZ	2-100w Med.	2194 BZ-GU24	1-18w GU24	2194 BZ-LED	1-17w LLH-100	6¾"	9¼"	4½" Square Back Plate		TT
2195 BZ	2-100w Med.	2195 BZ-GU24	2-18w GU24	2195 BZ-LED	1-17w LLH-100 & 1-8.5w LLH-60	6¾"	12½"	4½" Square Back Plate		TT

For posts and pier mounts, see pages 748-749.

CASTELLE™

FINISH BLACK

GLASS RIBBED ETCHED CYLINDER AND ETCHED CORNER PANELS

Castelle's transitional style in cast aluminum features clean lines and a ribbed etched glass cylinder accented by etched corner panels, adding to its sophisticated look.



1395 BK
1395 BK-GU24
1395 BK-LED
7" W, 18" H





1392 BK
1392 BK-GU24
1392 BK-LED
7" W, 15¾" H



1390 BK
1390 BK-GU24
1390 BK-LED
6" W, 15" H



1394 BK
1394 BK-GU24
1394 BK-LED
7" W, 13¾" H



1396 BK
1396 BK-GU24
1396 BK-LED
6" W, 11½" H



PIER MOUNT
1397 BK
1397 BK-GU24
1397 BK-LED
8½" W, 12¾" H



1391 BK
1391 BK-GU24
1391 BK-LED
7" W, 16½" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1390 BK	1-100w Med.	1390 BK-GU24	1-26w GU24	1390 BK-LED	1-15w LESM-100	7"	6¼"	4¼" W, 12¼" H Back Plate		BZ
1391 BK	1-100w Med.	1391 BK-GU24	1-26w GU24	1391 BK-LED	1-15w LESM-100			3" Dia. Post Fitter		BZ
1392 BK	1-100w Med.	1392 BK-GU24	1-26w GU24	1392 BK-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	BZ
1394 BK	1-100w Med.	1394 BK-GU24	1-26w GU24	1394 BK-LED	1-15w LESM-100	8¼"	5¾"	4¾" W, 10¼" H Back Plate		BZ
1395 BK	1-100w Med.	1395 BK-GU24	1-26w GU24	1395 BK-LED	1-15w LESM-100	8¼"	7"	4¾" W, 15" H Back Plate		BZ
1396 BK	1-75w Med.	1396 BK-GU24	1-18w GU24	1396 BK-LED	1-15w LESM-100	7"	4¾"	4¼" W, 8¾" H Back Plate		BZ
1397 BK	1-100w Med.	1397 BK-GU24	1-26w GU24	1397 BK-LED	1-15w LESM-100			8½" Square Base		BZ

For posts and pier mounts, see pages 748-749.

CASTELLE™

FINISH BRONZE

GLASS RIBBED ETCHED CYLINDER AND ETCHED CORNER PANELS

Castelle's transitional style in cast aluminum features clean lines and a ribbed etched glass cylinder accented by etched corner panels, adding to its sophisticated look.



1395 BZ
1395 BZ-GU24
1395 BZ-LED
7" W, 18" H





1392 BZ
1392 BZ-GU24
1392 BZ-LED
7" W, 15¾" H
[Icons: Energy Star, Recycle, T24]



1390 BZ
1390 BZ-GU24
1390 BZ-LED
6" W, 15" H
[Icons: Energy Star, Recycle, T24]



1394 BZ
1394 BZ-GU24
1394 BZ-LED
7" W, 13¼" H
[Icons: Energy Star, Recycle, T24]



1396 BZ
1396 BZ-GU24
1396 BZ-LED
6" W, 11½" H
[Icons: Energy Star, Recycle, T24]



PIER MOUNT
1397 BZ
1397 BZ-GU24
1397 BZ-LED
8½" W, 12¾" H
[Icons: Energy Star, Recycle, T24]



1391 BZ
1391 BZ-GU24
1391 BZ-LED
7" W, 16½" H
[Icons: Energy Star, Recycle, T24]

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1390 BZ	1-100w Med.	1390 BZ-GU24	1-26w GU24	1390 BZ-LED	1-15w LESM-100	7"	6¼"	4¼" W, 12¼" H Back Plate		BK
1391 BZ	1-100w Med.	1391 BZ-GU24	1-26w GU24	1391 BZ-LED	1-15w LESM-100			3" Dia. Post Fitter		BK
1392 BZ	1-100w Med.	1392 BZ-GU24	1-26w GU24	1392 BZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	BK
1394 BZ	1-100w Med.	1394 BZ-GU24	1-26w GU24	1394 BZ-LED	1-15w LESM-100	8¼"	5¾"	4¾" W, 10¼" H Back Plate		BK
1395 BZ	1-100w Med.	1395 BZ-GU24	1-26w GU24	1395 BZ-LED	1-15w LESM-100	8¼"	7"	4¾" W, 15" H Back Plate		BK
1396 BZ	1-75w Med.	1396 BZ-GU24	1-18w GU24	1396 BZ-LED	1-15w LESM-100	7"	4¾"	4¼" W, 8¾" H Back Plate		BK
1397 BZ	1-100w Med.	1397 BZ-GU24	1-26w GU24	1397 BZ-LED	1-15w LESM-100			8½" Square Base		BK

For posts and pier mounts, see pages 748-749.

CORDILLERA™

FINISH BUCKEYE BRONZE
GLASS ETCHED

Cordillera conveys contemporary chic with tall tubular glass, three-quarter trim rings and dramatic scaling. Solid aluminum construction and a Buckeye Bronze finish is paired with etched glass to complete this bold design.

Cordillera Chandelier, pages 100-101



1699 KZ
1699 KZ-GU24
1699 KZ-LED
4¾" W, 24" H






1698 KZ
1698 KZ-GU24
1698 KZ-LED
4¾" W, 18" H







1696 KZ
1696 KZ-GU24
1696 KZ-LED
4½" W, 16" H






1697 KZ
1697 KZ-GU24
1697 KZ-LED
7¾" W, 23" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
1696 KZ	1-75w Med.	1696 KZ-GU24	1-18w GU24	1696 KZ-LED	1-15w LESM-100	7½"	8"	4½" W, 11" H Back Plate
1697 KZ	1-100w Med.	1697 KZ-GU24	1-18w GU24	1697 KZ-LED	1-15w LESM-100			3" Dia. Post Fitter
1698 KZ	1-100w Med.	1698 KZ-GU24	1-18w GU24	1698 KZ-LED	1-15w LESM-100	8½"	9"	4½" W, 11" H Back Plate
1699 KZ	1-100w Med.	1699 KZ-GU24	1-18w GU24	1699 KZ-LED	1-15w LESM-100	8½"	12"	4½" W, 11" H Back Plate

For posts and pier mounts, see pages 748-749.

Elm's nature-inspired design offers an organic feel with hand-made sculptural detailing set against a backdrop of elegant distressed etched amber glass.

ELM™

REGENCY BRONZE FINISH
DISTRESSED ETCHED AMBER GLASS






1152 RB
1152 RB-GU24
1152 RB-LED
8¼" W, 17½" H






POCKET WALL MOUNT

1150 RB
1150 RB-GU24
1150 RB-LED
8" W, 10" H







POCKET WALL MOUNT


1155 RB
1155 RB-GU24
1155 RB-LED
11" W, 18" H






POCKET WALL MOUNT



1154 RB
1154 RB-GU24
1154 RB-LED
9" W, 14" H






1151 RB
(shown as pier mount
with 1304 RB)*



1151 RB
1151 RB-GU24
1151 RB-LED
9" DIA., 19" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1150 RB	1-100w Med.	1150 RB-GU24	1-18w GU24	1150 RB-LED	1-15w LESM-100	5½"	5"	8" W, 10" H Back Plate	
1151 RB	1-100w Med.	1151 RB-GU24	1-18w GU24	1151 RB-LED	1-15w LESM-100			3" Dia. Post Fitter	
1152 RB	1-100w Med.	1152 RB-GU24	1-18w GU24	1152 RB-LED	1-15w LESM-100			6½" Dia. Canopy	6', 5'
1154 RB	1-100w Med.	1154 RB-GU24	1-18w GU24	1154 RB-LED	1-15w LESM-100	5½"	7"	9" W, 14" H Back Plate	
1155 RB	1-100w Med.	1155 RB-GU24	1-18w GU24	1155 RB-LED	1-15w LESM-100	7"	9"	11" W, 18" H Back Plate	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 748-749.

LEDGEWOOD™

FINISH VINTAGE BLACK
GLASS CASÉD OPAL



Ledgewood path lights are available in the Hinkley Landscape Lighting catalog.

Ledgewood's bold cast aluminum construction features a unique oval shaped, overscaled design with elegant, clean line details.



1129 VK
1129 VK-GU24
1129 VK-LED
13" W, 19½" H





1122 VK
1122 VK-GU24
1122 VK-LED
13" W, 19¾" H






1124 VK
1124 VK-GU24
1124 VK-LED
8" W, 12" H






1125 VK
1125 VK-GU24
1125 VK-LED
10" W, 15½" H






1126 VK
1126 VK-GU24
1126 VK-LED
6½" W, 7¼" H






1120 VK
1120 VK-GU24
1120 VK-LED
7½" W, 10½" H






1121 VK
1121 VK-GU24
1121 VK-LED
13" W, 20¾" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1120 VK*	1-60w Med.	1120 VK-GU24*	1-13w GU24	1120 VK-LED	1-15w LESM-100	6½"	6"	4½" W, 7" H Back Plate		MR
1121 VK	1-100w Med.	1121 VK-GU24	1-26w GU24	1121 VK-LED	1-15w LESM-100			3" Dia. Post Fitter		MR
1122 VK*	1-100w Med.	1122 VK-GU24*	1-26w GU24	1122 VK-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	MR
1124 VK*	1-75w Med.	1124 VK-GU24*	1-18w GU24	1124 VK-LED	1-15w LESM-100	7¼"	6¾"	4½" W, 10" H Back Plate		MR
1125 VK*	1-100w Med.	1125 VK-GU24*	1-26w GU24	1125 VK-LED	1-15w LESM-100	9¼"	8¾"	4½" W, 10" H Back Plate		MR
1126 VK*	1-60w Med.	1126 VK-GU24*	1-13w GU24	1126 VK-LED	1-15w LESM-100	6"	3¾"	4½" W, 5½" H Back Plate		MR
1129 VK*	1-100w Med.	1129 VK-GU24*	1-26w GU24	1129 VK-LED	1-15w LESM-100	11¼"	11"	5" W, 13" H Back Plate		MR

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

LEDGEWOOD™

FINISH MUSEUM BRONZE
GLASS CHAMPAGNE INSIDE-ETCHED



LedgeWood path lights are available in the HinkleyLandscape Lighting catalog.

LedgeWood's bold cast aluminum construction features a unique oval shaped, overscaled design with elegant, clean line details.



1129 MR
1129 MR-GU24
1129 MR-LED
13" W, 19½" H





1122 MR
1122 MR-GU24
1122 MR-LED
13" W, 19¾" H







1124 MR
1124 MR-GU24
1124 MR-LED
8" W, 12" H







1125 MR
1125 MR-GU24
1125 MR-LED
10" W, 15½" H





1126 MR
1126 MR-GU24
1126 MR-LED
6½" W, 7¼" H





1120 MR
1120 MR-GU24
1120 MR-LED
7½" W, 10½" H





1121 MR
1121 MR-GU24
1121 MR-LED
13" W, 20¾" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1120 MR*	1-60w Med.	1120 MR-GU24*	1-13w GU24	1120 MR-LED	1-15w LESM-100	6½"	6"	4½" W, 7" H Back Plate		VK
1121 MR	1-100w Med.	1121 MR-GU24	1-26w GU24	1121 MR-LED	1-15w LESM-100			3" Dia. Post Fitter		VK
1122 MR*	1-100w Med.	1122 MR-GU24*	1-26w GU24	1122 MR-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	VK
1124 MR*	1-75w Med.	1124 MR-GU24*	1-18w GU24	1124 MR-LED	1-15w LESM-100	7¼"	6¾"	4½" W, 10" H Back Plate		VK
1125 MR*	1-100w Med.	1125 MR-GU24*	1-26w GU24	1125 MR-LED	1-15w LESM-100	9¼"	8¾"	4½" W, 10" H Back Plate		VK
1126 MR*	1-60w Med.	1126 MR-GU24*	1-13w GU24	1126 MR-LED	1-15w LESM-100	6"	3¾"	4½" W, 5½" H Back Plate		VK
1129 MR*	1-100w Med.	1129 MR-GU24*	1-26w GU24	1129 MR-LED	1-15w LESM-100	11¼"	11"	5" W, 13" H Back Plate		VK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.



“I love outdoor lanterns that have interesting angles, planes and scale. Looking at the chain detail and any closure or hinging also helps swing my decision!”

HEATHER GARRETT
HEATHER GARRETT INTERIOR DESIGN
DURHAM, NC

Pullman's mid-century modern design combines elements of a theater stage light with a dash of nautical chic. Pullman may be tilted for added flexibility. Pullman comes standard Dark Sky Compliant. Pullman pendants, page 275

PULLMAN™


OIL RUBBED BRONZE FINISH



2214 OZ
2214 OZ-GU24
2214 OZ-LED
10" W, 13½" H


THE SUGGESTION - Customize positioning with each Pullman fixtures' BOX
BOX 10° pivoting capability



2210 OZ
2210 OZ-GU24
2210 OZ-LED
7¼" W, 10½" H


ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2210 OZ	1-100w Med.	2210 OZ-GU24	1-26w GU24	2210 OZ-LED	1-15w LESM-100	8¼"	4¼"	4½" W, 8¼" H	GS
2214 OZ	1-100w Med.	2214 OZ-GU24	1-26w GU24	2214 OZ-LED	1-15w LESM-100	10¾"	4¼"	4½" W, 8¼" H	GS

PULLMAN™

FINISH GREYSTONE

Pullman's mid-century modern design combines elements of a theater stage light with a dash of nautical chic. Pullman may be tilted for added flexibility. Pullman comes standard Dark Sky Compliant.

Pullman pendants, page 275



2214 GS
2214 GS-GU24
2214 GS-LED
10" W, 13½" H




2210 GS
2210 GS-GU24
2210 GS-LED
7¼" W, 10½" H


ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2210 GS	1-100w Med.	2210 GS-GU24	1-26w GU24	2210 GS-LED	1-15w LESM-100	8¼"	4¼"	4½" W, 8¼" H	OZ
2214 GS	1-100w Med.	2214 GS-GU24	1-26w GU24	2214 GS-LED	1-15w LESM-100	10¾"	4¼"	4½" W, 8¼" H	OZ

Stanton's updated traditional lantern design in solid aluminum charms with authentic elements. A white linen center glass candle takes center stage and is enclosed by clear outer glass panels. Rivet and corner support details are accentuated by the rich finish.

STANTON™

OIL RUBBED BRONZE FINISH
CLEAR AND WHITE LINEN GLASS



2472 OZ
2472 OZ-LED
11" W, 19¼" H
T24



2475 OZ
2475 OZ-LED
11" W, 21¼" H
T24



2470 OZ
2470 OZ-LED
7½" W, 15½" H
T24



2474 OZ
2474 OZ-LED
9" W, 18¼" H
T24



2471 OZ
2471 OZ-LED
11" W, 20½" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
2470 OZ	1-100w Med.	2470 OZ-LED	1-15w LESM-100	9"	12"	4½" W, 7" H Back Plate	
2471 OZ	1-100w Med.	2471 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
2472 OZ	1-100w Med.	2472 OZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'
2474 OZ	1-100w Med.	2474 OZ-LED	1-15w LESM-100	10¾"	13¾"	4½" W, 9" H Back Plate	
2475 OZ	1-100w Med.	2475 OZ-LED	1-15w LESM-100	12¾"	12¼"	4½" W, 18¼" H Back Plate	

For posts and pier mounts, see pages 748-749.

SULLIVAN™

FINISH OIL RUBBED BRONZE
GLASS ETCHED OPAL

Sullivan's clean transitional style features a minimalist cast aluminum body that frames the contemporary, candle-like etched opal glass. A large cast ring finial is mounted on top for a traditional finishing touch to this sleek lantern design.



1745 OZ
1745 OZ-GU24
1745 OZ-LED
11¾" W, 23" H
Ⓢ Ⓜ T24

1742 BZ
1742 BZ-GU24
1742 BZ-LED
11¾" W, 23" H
Ⓢ Ⓜ T24

1741 OZ
1741 OZ-GU24
1741 OZ-LED
11¾" W, 26" H
Ⓢ Ⓜ T24

1744 OZ
1744 OZ-GU24
1744 OZ-LED
9" W, 18¼" H
Ⓢ Ⓜ T24

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1741 OZ	1-100w Med.	1741 OZ-GU24	1-13w GU24	1741 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter		BK
1742 OZ*	1-100w Med.	1742 OZ-GU24*	1-13w GU24	1742 OZ-LED	1-15w LESM-100			4½" Square Canopy	6', 5'	BK
1744 OZ	1-100w Med.	1744 OZ-GU24	1-13w GU24	1744 OZ-LED	1-15w LESM-100	10"	11¾"	5" W, 11¾" H Back Plate		BK
1745 OZ	1-100w Med.	1745 OZ-GU24	1-13w GU24	1745 OZ-LED	1-15w LESM-100	12¾"	15¼"	5" W, 15¼" H Back Plate		BK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Sullivan's clean transitional style features a minimalist cast aluminum body that frames the contemporary, candle-like etched opal glass. A large cast ring finial is mounted on top for a traditional finishing touch to this sleek lantern design.

SULLIVAN™

BLACK FINISH
ETCHED OPAL GLASS



1742 BK
1742 BK-GU24
1742 BK-LED
11¾" W, 23" H



1745 BK
1745 BK-GU24
1745 BK-LED
11¾" W, 23" H



1744 BK
1744 BK-GU24
1744 BK-LED
9" W, 18¼" H



1741 BK
1741 BK-GU24
1741 BK-LED
11¾" W, 26" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1741 BK	1-100w Med.	1741 BK-GU24	1-13w GU24	1741 BK-LED	1-15w LESM-100			3" Dia. Post Fitter		OZ
1742 BK*	1-100w Med.	1742 BK-GU24*	1-13w GU24	1742 BK-LED	1-15w LESM-100			4½" Square Canopy	6', 5'	OZ
1744 BK	1-100w Med.	1744 BK-GU24	1-13w GU24	1744 BK-LED	1-15w LESM-100	10"	11¾"	5" W, 11¾" H Back Plate		OZ
1745 BK	1-100w Med.	1745 BK-GU24	1-13w GU24	1745 BK-LED	1-15w LESM-100	12¾"	15¼"	5" W, 15¼" H Back Plate		OZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

QUINCY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Quincy's traditional bell-shaped design in die cast aluminum construction evokes early Americana. The seedy outer glass and interior etched opal cylinder, acting as a "faux" candle, adds to its nostalgic feel.

OBJECT OF OUR

AFFECTION

The essence of candlelight adds a warm glow to any exterior.



2618 OZ
2618 OZ-LED
11" W, 20" H





2612 OZ
2612 OZ-LED
9¼" W, 15½" H
T24



2615 OZ
2615 OZ-LED
9¼" W, 16¾" H
T24



2614 OZ
2614 OZ-LED
6¾" W, 13½" H
T24



2611 OZ
2611 OZ-LED
9¼" W, 18¾" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2611 OZ	1-100w Med.	2611 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
2612 OZ	1-100w Med.	2612 OZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'
2614 OZ	1-100w Med.	2614 OZ-LED	1-15w LESM-100	8¼"	7¾"	4¾" W, 11¾" H Back Plate	
2615 OZ	1-100w Med.	2615 OZ-LED	1-15w LESM-100	10¾"	9¼"	4¾" W, 15¼" H Back Plate	
2618 OZ	1-100w Med.	2618 OZ-LED	1-15w LESM-100	12½"	10¾"	4¾" W, 18½" H Back Plate	

For posts and pier mounts, see pages 748-749.

RILEY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY AND ETCHED OPAL (INNER)

Riley's shallow roof, arm and metal scroll bring a refined Arts & Crafts element to its aluminum construction. The seedy outer glass and inner etched opal glass offer a unique 'layered light' effect.



2015 OZ
2015 OZ-GU24
2015 OZ-LED
11" W, 18¾" H
Ⓢ Ⓡ Ⓣ24



2010 OZ
2010 OZ-GU24
2010 OZ-LED
9" W, 17½" H
Ⓢ Ⓡ Ⓣ24



2012 OZ
2012 OZ-GU24
2012 OZ-LED
11" DIA., 14" H
Ⓢ Ⓡ Ⓣ24



2011 OZ
2011 OZ-GU24
2011 OZ-LED
11" DIA., 18½" H
Ⓢ Ⓡ Ⓣ24



2014 OZ
2014 OZ-GU24
2014 OZ-LED
10" W, 18¼" H
Ⓢ Ⓡ Ⓣ24

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2010 OZ*	1-100w Med.	2010 OZ-GU24*	1-26w GU24	2010 OZ-LED	1-15w LESM-100	10¾"	7¾"	6½" Dia. Back Plate	
2011 OZ	1-100w Med.	2011 OZ-GU24	1-26w GU24	2011 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
2012 OZ*	1-100w Med.	2010 OZ-GU24*	1-26w GU24	2012 OZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'
2014 OZ*	1-100w Med.	2010 OZ-GU24*	1-26w GU24	2014 OZ-LED	1-15w LESM-100	11¾"	8"	6½" Dia. Back Plate	
2015 OZ*	1-100w Med.	2010 OZ-GU24*	1-26w GU24	2015 OZ-LED	1-15w LESM-100	12¾"	8½"	6½" Dia. Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Calistoga's historically-inspired design combines the vintage appeal of a classic pioneer lantern with updated lines and construction. This solid aluminum collection features a rich Spanish Bronze finish and clear seedy glass globe for authentic charm.

CALISTOGA™

SPANISH BRONZE FINISH
CLEAR SEEDY GLASS



2092 SB
2092 SB-LED
9¾" W, 16¼" H
T24

2095 SB
2095 SB-LED
9¾" W, 18¾" H
T24

2090 SB
2090 SB-LED
8½" W, 16¼" H
T24

2094 SB
2094 SB-LED
9" W, 17¾" H
T24

2091 SB
2091 SB-LED
9¾" W, 26" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2090 SB	1-100w Med.	2090 SB-LED	1-15w LESM-100	9¾"	7¼"	6" Dia. Back Plate	
2091 SB	1-100w Med.	2091 SB-LED	1-15w LESM-100			3" Dia. Post Fitter	
2092 SB	1-100w Med.	2092 SB-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'
2094 SB	1-100w Med.	2094 SB-LED	1-15w LESM-100	9¾"	7¼"	6" Dia. Back Plate	
2095 SB	1-100w Med.	2095 SB-LED	1-15w LESM-100	9¾"	7¼"	6" Dia. Back Plate	

When fitted with DSL-40, Calistoga fixtures are Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

NEW CASTLE™

FINISH BLACK
GLASS CLEAR SEEDY

The New Castle collection gives this traditional lantern design a modern twist with a recessed light source inside a seedy glass cylinder. The solid aluminum construction in a durable powder coat Black finish is Dark Sky compliant.



2258 BK
11" W, 24" H





2252 BK
11" DIA., 15" H



2254 BK
9" W, 16³/₄" H



2250 BK
7" W, 9³/₄" H



2255 BK
11" W, 19¹/₂" H



2251 BK
11" W, 22¹/₄" H



ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2250 BK	1-35w GU-10*	8"	5 ³ / ₄ "	4 ¹ / ₂ " W, 6 ³ / ₄ " H Back Plate	6', 5'
2251 BK	1-50w GU-10*			3" Dia. Post Fitter	
2252 BK	1-50w GU-10*	5 ¹ / ₂ " Dia. Canopy			
2254 BK	1-50w GU-10*	10"	11"	4 ¹ / ₂ " W, 6 ³ / ₄ " H Back Plate	
2255 BK	1-50w GU-10*	12 ¹ / ₄ "	12 ¹ / ₄ "	4 ¹ / ₂ " W, 6 ³ / ₄ " H Back Plate	
2258 BK	1-50w GU-10*	12 ¹ / ₄ "	12 ¹ / ₄ "	4 ¹ / ₂ " W, 6 ³ / ₄ " H Back Plate	

*GU-10 bulbs included. For posts and pier mounts, see pages 748-749.

BELDEN PLACE™

FINISH OIL RUBBED BRONZE
GLASS CLEAR

Belden Place offers stylish simplicity with a dash of nautical elegance in durable solid aluminum construction. Its clean lines offer a modern take on a vintage gas lantern.



2865 OZ
12" W, 19¼" H



2862 OZ
10" W, 16½" H
49" MAX. H*



2864 OZ
10" W, 16" H



2860 OZ
8" W, 11" H



2861 OZ
(shown as pier mount
with 1304 OZ)**



2861 OZ
12" W, 22" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2860 OZ***	1-100w Med.	9"	3¾"	4½" W, 7¼" H Back Plate		
2861 OZ	1-100w Med.			3" Dia. Post Fitter		
2862 OZ***	1-100w Med.			6" Dia. Canopy	10'	1-6", 2-12"
2864 OZ***	1-100w Med.	11"	4½"	4½" W, 7¼" H Back Plate		
2865 OZ***	1-100w Med.	13"	4½"	4½" W, 7¼" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 4312OZ. **Not for use within 4 ft. of ground. ***When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

CAPE COD™

FINISH SIENNA BRONZE
GLASS CLEAR SEEDY

Cape Cod's classic onion lantern design conveys classic New England style. The solid brass construction and clear seedy glass add vintage appeal.



2205 SZ
2205 SZ-LED
14" W, 26¾" H





2202 SZ
2202 SZ-LED
11" DIA., 18" H
T24



2203 SZ
2203 SZ-LED
7" W, 9" H
T24



2200 SZ
2200 SZ-LED
8¾" W, 18" H
T24



2206 SZ
2206 SZ-LED
7¼" W, 14" H
T24



2204 SZ
2204 SZ-LED
11" W, 23¼" H
T24



2207 SZ
2207 SZ-LED
11¼" DIA., 21¼" H
T24



2201 SZ
2201 SZ-LED
14" DIA., 23¾" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2200 SZ*	1-75w Med.	2200 SZ-LED	1-15w LESM-100	10¼"	11½"	4¼" W, 5½" H Back Plate		DZ
2201 SZ	4-40w Cand.	2201 SZ-LED	1-15w LESM-100			3" Dia. Post Fitter		DZ
2202 SZ*	1-100w Med.	2202 SZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	DZ
2203 SZ*	1-60w Med.	2203 SZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	DZ
2204 SZ*	1-100w Med.	2204 SZ-LED	1-15w LESM-100	13"	16"	4½" W, 9½" H Back Plate		DZ
2205 SZ*	1-100w Med.	2205 SZ-LED	1-15w LESM-100	15"	17"	4½" W, 10" H Back Plate		DZ
2206 SZ*	1-60w Med.	2206 SZ-LED	1-15w LESM-100	8"	9¼"	4½" W, 5½" H Back Plate		DZ
2207 SZ	3-40w Cand.	2207 SZ-LED	1-15w LESM-100			3" Dia. Post Fitter		DZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

CAPE COD™

FINISH AGED ZINC
GLASS CLEAR SEEDY

Cape Cod's classic onion lantern design conveys classic New England style. The aluminum construction and clear seedy glass add vintage appeal.



2205 DZ
2205 DZ-LED
14" W, 26¾" H





2202 DZ
2202 DZ-LED
11" DIA., 18" H
T24



2203 DZ
2203 DZ-LED
7" W, 9" H
T24



2200 DZ
2200 DZ-LED
8¾" W, 18" H
T24



2206 DZ
2206 DZ-LED
7¼" W, 14" H
T24



2204 DZ
2204 DZ-LED
11" W, 23¾" H
T24



2207 DZ
2207 DZ-LED
11¼" DIA., 21¼" H
(shown as pier mount
with 1304 DZ)*
T24



2201 DZ
2201 DZ-LED
14" DIA., 23¾" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2200 DZ**	1-75w Med.	2200 DZ-LED	1-15w LESM-100	10¼"	11½"	4¼" W, 5½" H Back Plate		SZ
2201 DZ	4-40w Cand.	2201 DZ-LED	1-15w LESM-100			3" Dia. Post Fitter		SZ
2202 DZ**	1-100w Med.	2202 DZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	SZ
2203 DZ**	1-60w Med.	2203 DZ-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'	SZ
2204 DZ**	1-100w Med.	2204 DZ-LED	1-15w LESM-100	13"	16"	4½" W, 9½" H Back Plate		SZ
2205 DZ**	1-100w Med.	2205 DZ-LED	1-15w LESM-100	15"	17"	4½" W, 10" H Back Plate		SZ
2206 DZ**	1-60w Med.	2206 DZ-LED	1-15w LESM-100	8"	9¼"	4½" W, 5½" H Back Plate		SZ
2207 DZ	3-40w Cand.	2207 DZ-LED	1-15w LESM-100			3" Dia. Post Fitter		SZ

*Not for use within 4 ft. of ground. **When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

FREEPORT™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.



1804 OZ
1804 OZ-GU24
1804 OZ-LED
8" W, 12¼" H
☞ ☻ T24



1800 OZ
1800 OZ-GU24
1800 OZ-LED
6" W, 9¼" H
☞ ☻ T24



1801 OZ
1801 OZ-GU24
1801 OZ-LED
10" DIA., 20¼" H
☞ ☻ T24



1805 OZ
1805 OZ-GU24
1805 OZ-LED
10" W, 15¼" H
☞ ☻ T24



1802 OZ
1802 OZ-GU24
1802 OZ-LED
10" DIA., 14" H
☞ ☻ T24

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1800 OZ*	1-75w Med.	1800 OZ-GU24*	1-18w GU24	1800 OZ-LED	1-10w UNI-60	7"	2½"	4½" W, 6" H Back Plate		BK, OP
1801 OZ	1-100w Med.	1801 OZ-GU24	1-26w GU24	1801 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter		BK, OP
1802 OZ*	1-100w Med.	1800 OZ-GU24*	1-26w GU24	1800 OZ-LED	1-15w UNI-100			4¼" Dia. Canopy	6', 5'	BK, OP
1804 OZ*	1-100w Med.	1804 OZ-GU24*	1-26w GU24	1804 OZ-LED	1-15w UNI-100	9"	3"	5" W, 8" H Back Plate		BK, OP
1805 OZ*	1-100w Med.	1800 OZ-GU24*	1-26w GU24	1800 OZ-LED	1-15w UNI-100	11¼"	3¼"	5¾" W, 9½" H Back Plate		BK, OP

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

FREEPORT™

BLACK FINISH
CLEAR SEEDY GLASS



1800 BK
1800 BK-GU24
1800 BK-LED
6" W, 9¼" H



1804 BK
1804 BK-GU24
1804 BK-LED
8" W, 12¼" H



1802 BK
1802 BK-GU24
1802 BK-LED
10" DIA., 14" H



1805 BK
1805 BK-GU24
1805 BK-LED
10" W, 15¼" H



1801 BK
1801 BK-GU24
1801 BK-LED
10" DIA., 20¼" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1800 BK*	1-75w Med.	1800 BK-GU24*	1-18w GU24	1800 BK-LED	1-10w UNI-60	7"	2½"	4½" W, 6" H Back Plate		OP, OZ
1801 BK	1-100w Med.	1801 BK-GU24	1-26w GU24	1801 BK-LED	1-15w LESM-100			3" Dia. Post Fitter		OP, OZ
1802 BK*	1-100w Med.	1800 BK-GU24*	1-26w GU24	1800 BK-LED	1-15w UNI-100			4¼" Dia. Canopy	6', 5'	OP, OZ
1804 BK*	1-100w Med.	1804 BK-GU24*	1-26w GU24	1804 BK-LED	1-15w UNI-100	9"	3"	5" W, 8" H Back Plate		OP, OZ
1805 BK*	1-100w Med.	1800 BK-GU24*	1-26w GU24	1800 BK-LED	1-15w UNI-100	11¼"	3¼"	5¾" W, 9½" H Back Plate		OP, OZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

FREEPORT™

FINISH OLDE PENNY
GLASS ETCHED SEEDY

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.



1804 OP
1804 OP-GU24
1804 OP-LED
8" W, 12¼" H
[Energy Star] [Recycle] [T24]



1800 OP
1800 OP-GU24
1800 OP-LED
6" W, 9¼" H
[Energy Star] [Recycle] [T24]



1801 OP
1801 OP-GU24
1801 OP-LED
10" DIA., 20¼" H
[Energy Star] [Recycle] [T24]



1805 OP
1805 OP-GU24
1805 OP-LED
10" W, 15¼" H
[Energy Star] [Recycle] [T24]



1802 OP
1802 OP-GU24
1802 OP-LED
10" W, 14" H
[Energy Star] [Recycle] [T24]

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1800 OP*	1-75w Med.	1800 OP-GU24*	1-18w GU24	1800 OP-LED	1-15w LESM-100	7"	2½"	4½" W, 6" H Back Plate		BK, OZ
1801 OP	1-100w Med.	1801 OP-GU24	1-26w GU24	1801 OP-LED	1-15w LESM-100			3" Dia. Post Fitter		BK, OZ
1802 OP*	1-100w Med.	1800 OP-GU24*	1-26w GU24	1800 OP-LED	1-15w LESM-100			4¼" Dia. Canopy	6', 5'	BK, OZ
1804 OP*	1-100w Med.	1804 OP-GU24*	1-26w GU24	1804 OP-LED	1-15w LESM-100	9"	3"	5" W, 8" H Back Plate		BK, OZ
1805 OP*	1-100w Med.	1800 OP-GU24*	1-26w GU24	1800 OP-LED	1-15w LESM-100	11¼"	3¼"	5¾" W, 9½" H Back Plate		BK, OZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Pembrook is a classic, all-American style traditional hanging wall lantern featuring solid aluminum construction with cast ball knob detailing and acorn shaped glass.

PEMBROOK™

SPANISH BRONZE FINISH
ETCHED OPAL GLASS



2082 SB
2082 SB-LED
10" DIA., 14¾" H



2084 SB
2084 SB-LED
12" W, 15¾" H



2080 SB
2080 SB-LED
10" W, 13¾" H



2081 SB
2081 SB-LED
13¾" W, 18" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2080 SB	1-100w Med.	2080 SB-LED	1-15w UNI-100	10½"	4¼"	6" Dia. Back Plate	
2081 SB	1-100w Med.	2081 SB-LED	1-15w UNI-100			3" Dia. Post Fitter	
2082 SB	1-100w Med.	2082 SB-LED	1-15w UNI-100			6" Dia. Canopy	6', 5'
2084 SB	1-100w Med.	2084 SB-LED	1-15w UNI-100	13"	4¼"	6" Dia. Back Plate	




When fitted with DSL-40, Pembrook fixtures are Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

REEF™




FINISH HEMATITE
GLASS INSIDE ETCHED

Reef's contemporary nautical shape features a sleek capsule of inside etched glass captured by bold rings of cast aluminum.






1956 HE
1956 HE-GU24
1956 HE-LED
5½" W, 8" H









1950 HE
1950 HE-GU24
1950 HE-LED
7¾" W, 10¾" H









1951 HE
1951 HE-GU24
1951 HE-LED
9" DIA., 16¼" H
(shown as pier mount
with 1304 OZ)*






1954 HE
1954 HE-GU24
1954 HE-LED
9" W, 12¾" H






1952 HE
1952 HE-GU24
1952 HE-LED
9" DIA., 15" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1950 HE**	1-75w Med.	1950 HE-GU24**	1-13w GU24	1950 HE-LED	1-15w LESM-100	8¾"	4"	4½" W, 7" H Back Plate		VZ
1951 HE	1-100w Med.	1951 HE-GU24	1-18w GU24	1951 HE-LED	1-15w LESM-100			3" Dia. Post Fitter		VZ
1952 HE**	1-100w Med.	1952 HE-GU24**	1-18w GU24	1952 HE-LED	1-15w LESM-100			5½" Dia. Canopy	6', 5'	VZ
1954 HE**	1-100w Med.	1954 HE-GU24**	1-18w GU24	1954 HE-LED	1-15w LESM-100	10"	4¼"	4½" W, 7" H Back Plate		VZ
1956 HE**	1-60w Med.	1956 HE-GU24**	1-13w GU24	1956 HE-LED	1-15w LESM-100	6½"	2¾"	4½" W, 5¼" H Back Plate		VZ

*Not for use within 4 ft. of ground. **When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Reef's contemporary nautical shape features a sleek capsule of inside etched glass captured by bold rings of cast aluminum.

REEF™

VICTORIAN BRONZE FINISH
INSIDE ETCHED GLASS



1952 VZ
1952 VZ-GU24
1952 VZ-LED
9" DIA., 15" H
[Energy Efficient] [Recycled] [T24]



1950 VZ
1950 VZ-GU24
1950 VZ-LED
7¾" W, 10¾" H
[Energy Efficient] [Recycled] [T24]



1956 VZ
1956 VZ-GU24
1956 VZ-LED
5½" W, 8" H
[Energy Efficient] [Recycled] [T24]



1954 VZ
1954 VZ-GU24
1954 VZ-LED
9" W, 12¾" H
[Energy Efficient] [Recycled] [T24]



1951 VZ
1951 VZ-GU24
1951 VZ-LED
9" DIA., 16¾" H
[Energy Efficient] [Recycled] [T24]

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1950 VZ*	1-75w Med.	1950 VZ-GU24*	1-13w GU24	1950 VZ-LED	1-15w LESM-100	8¾"	4"	4½" W, 7" H Back Plate		HE
1951 VZ	1-100w Med.	1951 VZ-GU24	1-18w GU24	1951 VZ-LED	1-15w LESM-100			3" Dia. Post Fitter		HE
1952 VZ*	1-100w Med.	1952 VZ-GU24*	1-18w GU24	1952 VZ-LED	1-15w LESM-100			5½" Dia. Canopy	6', 5'	HE
1954 VZ*	1-100w Med.	1954 VZ-GU24*	1-18w GU24	1954 VZ-LED	1-15w LESM-100	10"	4¼"	4½" W, 7" H Back Plate		HE
1956 VZ*	1-60w Med.	1956 VZ-GU24*	1-13w GU24	1956 VZ-LED	1-15w LESM-100	6½"	2¾"	4½" W, 5¼" H Back Plate		HE

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

BOLLA™

FINISH OLDE BRONZE
GLASS CLEAR SEEDY



Bolla path lights
are available
in the Hinkley
Landscape
Lighting Catalog

The graceful lines of Bolla create a soft elegance,
while the solid brass construction and heavy
cast ball transitions add to its innovative style.

Bolla Chandelier, pages 106-119
Bolla Bath, pages 461-463



2649 OB
14" W, 26" H



2642 OB
11" DIA., 20½" H



2643 OB
16¾" DIA., 8" H



2644 OB
9" W, 15¾" H



2645 OB
11" W, 18¾" H



2646 OB
6" W, 11" H



2640 OB
7¼" W, 12¼" H



2641 OB
11" DIA., 20½" H
(shown as pier mount
with 1304 OB)*

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2640 OB	1-60w Med.	9"	7"	4½" W, 7¼" H Back Plate	
2641 OB	3-40w Cand.			3" Dia. Post Fitter	
2642 OB	3-40w Cand.			5" Dia. Canopy	6', 5'
2643 OB	2-75w Med.				
2644 OB	2-40w Cand.	10½"	8"	4½" W, 7¼" H Back Plate	
2645 OB	3-40w Cand.	12½"	9¾"	4½" W, 9" H Back Plate	
2646 OB	1-60w Med.	6¾"	3"	5" W, 6" H Back Plate	
2649 OB	4-40w Cand.	16"	12¾"	4½" W, 11½" H Back Plate	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 748-749.

BOLLA™

FINISH OLDE BRONZE
GLASS LIGHT AMBER SEEDY



Bolla path lights
are available
in the Hinkley
Landscape
Lighting Catalog.

The graceful lines of Bolla create a soft elegance,
while the solid brass construction and heavy
cast ball transitions add to its innovative style.




Bolla Chandelier, pages 106-119
Bolla Bath, pages 461-463



2639 OB
2639 OB-GU24
2639 OB-LED
14" W, 26" H








2632 OB
2632 OB-GU24
2632 OB-LED
11" DIA., 20½" H









2633 OB
2633 OB-GU24
2633 OB-LED
16¾" DIA., 8" H







2634 OB
2634 OB-GU24
2634 OB-LED
9" W, 15¾" H









2635 OB
2635 OB-GU24
2635 OB-LED
11" W, 18¾" H







2636 OB
2636 OB-GU24
2636 OB-LED
6" W, 11" H







2630 OB
2630 OB-GU24
2630 OB-LED
7¼" W, 12¼" H






2631 OB
2631 OB-GU24
2631 OB-LED
11" DIA., 20½" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2630 OB	1-60w Med.	2630 OB-GU24	1-13w GU24	2630 OB-LED	1-15w LESM-100	9"	7"	4½" W, 7¼" H Back Plate	
2631 OB	3-40w Cand.	2631 OB-GU24	1-18w GU24	2631 OB-LED	1-15w LESM-100			3" Dia. Post Fitter	
2632 OB	3-40w Cand.	2632 OB-GU24	1-18w GU24	2632 OB-LED	1-15w LESM-100			5" Dia. Canopy	6', 5'
2633 OB	2-75w Med.	2633 OB-GU24	2-18w GU24	2633 OB-LED	1-32w FSI-200				
2634 OB	2-40w Cand.	2634 OB-GU24	1-18w GU24	2634 OB-LED	1-15w LESM-100	10½"	8"	4½" W, 7¼" H Back Plate	
2635 OB	3-40w Cand.	2635 OB-GU24	1-18w GU24	2635 OB-LED	1-15w LESM-100	12½"	9¾"	4½" W, 9" H Back Plate	
2636 OB	1-60w Med.	2636 OB-GU24	1-13w GU24	2636 OB-LED	1-15w LESM-100	6¾"	3"	5" W, 6" H Back Plate	
2639 OB	4-40w Cand.	2639 OB-GU24	4-13w GU24	2639 OB-LED	2-15w LESM-100	16"	12¾"	4½" W, 11½" H Back Plate	

For posts and pier mounts, see pages 748-749.

THISTLEDOWN™

FINISH VICTORIAN BRONZE
GLASS AMBER LINEN

Thistledown is an updated traditional design with smooth, flowing transitions that blend into an industrial yoke-mount center stem. Solid aluminum construction in a Victorian Bronze finish complements its amber linen glass for a warm elegance.

Thistledown Chandelier, pages 94-97



1285 VZ
1285 VZ-LED
12¾" W, 20½" H





1282 VZ
1282 VZ-LED
12¾" W, 20¾" H
T24



4171 VZ
4171 VZ-LED
15¼" DIA., 8" H
T24



1280 VZ
1280 VZ-LED
8½" W, 13¼" H
T24



1286 VZ
1286 VZ-LED
6½" W, 9¾" H
T24



1284 VZ
1284 VZ-LED
10½" W, 16" H
T24



1281 VZ
1281 VZ-LED
12¾" W, 22½" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1280 VZ*	1-60w Med.	1280 VZ-LED	1-15w LESM-100	10"	7"	5" W, 9" H Back Plate	
1281 VZ	1-100w Med.	1281 VZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
1282 VZ*	1-100w Med.	1282 VZ-LED	1-15w LESM-100			5¾" Dia. Canopy	6', 5'
1284 VZ*	1-75w Med.	1284 VZ-LED	1-15w LESM-100	11½"	8½"	5" W, 9" H Back Plate	
1285 VZ*	1-100w Med.	1285 VZ-LED	1-15w LESM-100	14¾"	11"	5" W, 12" H Back Plate	
1286 VZ*	1-60w Med.	1286 VZ-LED	1-15w LESM-100	7½"	5¼"	5" W, 7" H Back Plate	
4171 VZ	3-60w Med.	4171 VZ-LED	1-32w FSI-200				

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

STRATFORD™

FINISH OIL RUBBED BRONZE
GLASS WHITE LINEN SEEDY PANELS

Stratford offers a classic tapered square design in sturdy cast aluminum with generous panels of seedy linen glass. The classic finish options complement a variety of exteriors.



1356 OZ
1356 OZ-GU24
1356 OZ-LED
6" W, 10¾" H
[Icons: Recycle, Energy Star, T24]



1354 OZ
1354 OZ-GU24
1354 OZ-LED
9½" W, 16" H
[Icons: Recycle, Energy Star, T24]



1352 OZ
1352 OZ-GU24
1352 OZ-LED
9½" W, 15½" H
[Icons: Recycle, Energy Star, T24]



1351 OZ
1351 OZ-GU24
1351 OZ-LED
9½" W, 21" H
[Icons: Recycle, Energy Star, T24]



1350 OZ
1350 OZ-GU24
1350 OZ-LED
7½" W, 12½" H
[Icons: Recycle, Energy Star, T24]

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1350 OZ*	1-60w Med.	1350 OZ-GU24*	1-13w GU24	1350 OZ-LED	1-15w LESM-100	8¾"	3½"	5¼" W, 8" H Back Plate		MB
1351 OZ	1-100w Med.	1351 OZ-GU24	1-26w GU24	1351 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter		MB
1352 OZ*	1-100w Med.	1352 OZ-GU24*	1-26w GU24	1352 OZ-LED	1-15w LESM-100			4¾" Dia. Canopy	6', 5'	MB
1354 OZ*	1-75w Med.	1354 OZ-GU24*	1-18w GU24	1354 OZ-LED	1-15w LESM-100	11"	3¾"	6" W, 9¾" H Back Plate		MB
1356 OZ*	1-60w Med.	1356 OZ-GU24*	1-13w GU24	1356 OZ-LED	1-15w LESM-100	7"	3"	4½" W, 6" H Back Plate		MB

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Stratford offers a classic tapered square design in sturdy cast aluminum with generous panels of seedy linen glass. The classic finish options complement a variety of exteriors.

STRATFORD™

MUSEUM BLACK FINISH
WHITE LINEN SEEDY PANELS GLASS



1352 MB
1352 MB-GU24
1352 MB-LED
9½" W, 15½" H
[Icons: Recycle, LED, T24]



1354 MB
1354 MB-GU24
1354 MB-LED
9½" W, 16" H
[Icons: Recycle, LED, T24]



1356 MB
1356 MB-GU24
1356 MB-LED
6" W, 10¾" H
[Icons: Recycle, LED, T24]



1350 MB
1350 MB-GU24
1350 MB-LED
7½" W, 12½" H
[Icons: Recycle, LED, T24]



1351 MB
1351 MB-GU24
1351 MB-LED
9½" W, 21" H
[Icons: Recycle, LED, T24]

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1350 MB*	1-60w Med.	1350 MB-GU24*	1-13w GU24	1350 MB-LED	1-15w LESM-100	8¾"	3½"	5¼" W, 8" H Back Plate		OZ
1351 MB	1-100w Med.	1351 MB-GU24	1-26w GU24	1351 MB-LED	1-15w LESM-100			3" Dia. Post Fitter		OZ
1352 MB*	1-100w Med.	1352 MB-GU24*	1-26w GU24	1352 MB-LED	1-15w LESM-100			4¾" Dia. Canopy	6', 5'	OZ
1354 MB*	1-75w Med.	1354 MB-GU24*	1-18w GU24	1354 MB-LED	1-15w LESM-100	11"	3¾"	6" W, 9¾" H Back Plate		OZ
1356 MB*	1-60w Med.	1356 MB-GU24*	1-13w GU24	1356 MB-LED	1-15w LESM-100	7"	3"	4½" W, 6" H Back Plate		OZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

CHERRY CREEK™

FINISH OIL RUBBED BRONZE
GLASS AMBER LINEN




Cherry Creek's modern take on the popular Arts & Crafts style has a timeless appeal. The cast aluminum construction is enhanced by the warmth of the finish and the vintage-looking amber linen glass.






1275 OZ
1275 OZ-GU24
1275 OZ-LED
12" W, 20½" H





1270 OZ
1270 OZ-GU24
1270 OZ-LED
6½" W, 11" H









1273 OZ
1273 OZ-GU24
1273 OZ-LED
12" W, 7¼" H






1272 OZ
1272 OZ-GU24
1272 OZ-LED
12" W, 20¾" H






1274 OZ
1274 OZ-GU24
1274 OZ-LED
8½" W, 15¼" H






1271 OZ
1271 OZ-GU24
1271 OZ-LED
12" W, 22¼" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	TOP TO EXT.	OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1270 OZ*	1-60w Med.	1270 OZ-GU24*	1-13w GU24	1270 OZ-LED	1-15w LESM-100	7¼"	4¼"	4½" W, 7" H Back Plate		VK
1271 OZ	1-100w Med.	1271 OZ-GU24	1-26w GU24	1271 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter		VK
1272 OZ*	1-100w Med.	1272 OZ-GU24*	1-26w GU24	1272 OZ-LED	1-15w LESM-100			5½" Dia. Canopy	6', 5'	VK
1273 OZ	2-60w Med.	1273 OZ-GU24	2-13w GU24	1273 OZ-LED	1-32w FSI-200					VK
1274 OZ*	1-75w Med.	1274 OZ-GU24*	1-18w GU24	1274 OZ-LED	1-15w LESM-100	9¼"	5"	4½" W, 10" H Back Plate		VK
1275 OZ*	1-100w Med.	1275 OZ-GU24*	1-26w GU24	1275 OZ-LED	1-15w LESM-100	12¾"	6½"	5" W, 13" H Back Plate		VK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

CHERRY CREEK™

FINISH VINTAGE BLACK
GLASS WHITE LINEN

Cherry Creek's modern take on the popular Arts & Crafts style has a timeless appeal. The cast aluminum construction is enhanced by the Black finish and the vintage-looking white linen glass.



1275 VK
1275 VK-GU24
1275 VK-LED
12" W, 20½" H





1270 VK
1270 VK-GU24
1270 VK-LED
6½" W, 11" H






1273 VK
1273 VK-GU24
1273 VK-LED
12" W, 7¼" H






1272 VK
1272 VK-GU24
1272 VK-LED
12" W, 20¾" H






1274 VK
1274 VK-GU24
1274 VK-LED
8½" W, 15¼" H






1271 VK
1271 VK-GU24
1271 VK-LED
12" W, 22¼" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	TOP TO EXT.	OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1270 VK*	1-60w Med.	1270 VK-GU24*	1-13w GU24	1270 VK-LED	1-15w LESM-100	7¼"	4¼"	4½" W, 7" H Back Plate		OZ
1271 VK	1-100w Med.	1271 VK-GU24	1-26w GU24	1271 VK-LED	1-15w LESM-100			3" Dia. Post Fitter		OZ
1272 VK*	1-100w Med.	1272 VK-GU24*	1-26w GU24	1272 VK-LED	1-15w LESM-100			5½" Dia. Canopy	6', 5'	OZ
1273 VK	2-60w Med.	1273 VK-GU24	2-13w GU24	1273 VK-LED	1-32w FSI-200					OZ
1274 VK*	1-75w Med.	1274 VK-GU24*	1-18w GU24	1274 VK-LED	1-15w LESM-100	9¼"	5"	4½" W, 10" H Back Plate		OZ
1275 VK*	1-100w Med.	1275 VK-GU24*	1-26w GU24	1275 VK-LED	1-15w LESM-100	12¾"	6½"	5" W, 13" H Back Plate		OZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

TUCKER™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Tucker is a study in symmetry with clean geometric lines and proportions reinforced throughout its cast aluminum construction. The sturdy Oil Rubbed Bronze finish and clear seedy glass inspire a rustic lodge aesthetic.



1965 OZ
11" W, 18" H



1962 OZ
11" W, 17½" H



1964 OZ
9" W, 14¾" H



1960 OZ
7" W, 11½" H



1961 OZ
11" W, 20½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1960 OZ*	1-100w Med.	8"	2½"	4½" W, 5½" H Back Plate	
1961 OZ	1-100w Med.			3" Dia. Post Fitter	
1962 OZ*	1-100w Med.			5" Dia. Canopy	6', 5'
1964 OZ*	1-100w Med.	10¼"	3½"	4½" W, 6¾" H Back Plate	
1965 OZ*	1-100w Med.	12¼"	3¾"	5½" W, 8¼" H Back Plate	




*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

CEDAR HILL™




FINISH OIL RUBBED BRONZE
GLASS AMBER LINEN

Cedar Hill is a traditional outdoor lantern in durable die cast aluminum construction with medium base lamping. This four-sided soft tapered design features linen glass behind arched window pane panels and is available in two popular finishes.



1984 OZ
1984 OZ-GU24
1984 OZ-LED
7¾" W, 12½" H









1982 OZ
1982 OZ-GU24
1982 OZ-LED
7¾" W, 13¾" H






1981 OZ
1981 OZ-GU24
1981 OZ-LED
7¾" W, 16" H






1980 OZ
1980 OZ-GU24
1980 OZ-LED
5¾" W, 9¼" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1980 OZ*	1-75w Med.	1980 OZ-GU24*	1-18w GU24	1980 OZ-LED	1-15w LESM-100	6¾"	4½"	4½" W, 6" H Back Plate		BK
1981 OZ	1-100w Med.	1981 OZ-GU24	1-26w GU24	1981 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter		BK
1982 OZ*	1-100w Med.	1982 OZ-GU24*	1-26w GU24	1982 OZ-LED	1-15w LESM-100			5¾" Square Canopy	6', 5'	BK
1984 OZ*	1-100w Med.	1984 OZ-GU24*	1-26w GU24	1984 OZ-LED	1-15w LESM-100	9¼"	5¾"	5¼" W, 8" H Back Plate		BK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Cedar Hill is a traditional outdoor lantern in durable die cast aluminum construction with medium base lamping. This four-sided soft tapered design features linen glass behind arched window pane panels and is available in two popular finishes.

CEDAR HILL™

BLACK FINISH
WHITE LINEN GLASS



1982 BK
1982 BK-GU24
1982 BK-LED
7¾" W, 13¾" H



1984 BK
1984 BK-GU24
1984 BK-LED
7¾" W, 12½" H



1980 BK
1980 BK-GU24
1980 BK-LED
5¾" W, 9¼" H



1981 BK
1981 BK-GU24
1981 BK-LED
7¾" W, 16" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1980 BK*	1-75w Med.	1980 BK-GU24*	1-18w GU24	1980 BK-LED	1-15w LESM-100	6¾"	4½"	4½" W, 6" H Back Plate		OZ
1981 BK	1-100w Med.	1981 BK-GU24	1-26w GU24	1981 BK-LED	1-15w LESM-100			3" Dia. Post Fitter		OZ
1982 BK*	1-100w Med.	1982 BK-GU24*	1-26w GU24	1982 BK-LED	1-15w LESM-100			5¾" Square Canopy	6', 5'	OZ
1984 BK*	1-100w Med.	1984 BK-GU24*	1-26w GU24	1984 BK-LED	1-15w LESM-100	9¼"	5¾"	5¾" W, 8" H Back Plate		OZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

DRAKE™

FINISH OIL RUBBED BRONZE
GLASS CLEAR INSIDE ETCHED SEEDY

The Drake collection is an updated traditional design in cast aluminum with a geometric "Y" pattern in the window pane as its focal point. This classic architectural detail encourages a subtle Mission style while creating an updated bound glass lantern look.






1995 OZ
1995 OZ-GU24
1995 OZ-LED
11½" W, 21" H








1992 OZ
1992 OZ-GU24
1992 OZ-LED
9½" W, 19¼" H






1994 OZ
1994 OZ-GU24
1994 OZ-LED
9½" W, 17½" H





1990 OZ
1990 OZ-GU24
1990 OZ-LED
7½" W, 13¾" H



1991 OZ
1991 OZ-GU24
1991 OZ-LED
9½" W, 20¾" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1990 OZ*	1-100w Med.	1990 OZ-GU24*	1-18w GU24	1990 OZ-LED	1-15w LESM-100	8¾"	5½"	5" W, 8" H Back Plate	
1991 OZ	1-100w Med.	1991 OZ-GU24	1-18w GU24	1991 OZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
1992 OZ*	1-100w Med.	1992 OZ-GU24*	1-18w GU24	1992 OZ-LED	1-15w LESM-100			5" Square Canopy	6', 5'
1994 OZ*	1-100w Med.	1994 OZ-GU24*	1-18w GU24	1994 OZ-LED	1-15w LESM-100	10¾"	7"	6¼" W, 10¼" H Back Plate	
1995 OZ*	1-100w Med.	1995 OZ-GU24*	1-18w GU24	1995 OZ-LED	1-15w LESM-100	13"	8¼"	7" W, 10¾" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

HOLBROOK™

FINISH BLACK
GLASS CLEAR SEEDY

Holbrook features a tall, slim silhouette with aluminum construction and a simple Black finish with modest design elements. The dense, seedy glass complements its updated Arts & Crafts style, creating a new classic in outdoor lanterns.



1794 BK
1794 BK-GU24
11" W, 18" H





1792 BK
1792 BK-GU24
11" W, 19¼" H



POCKET WALL MOUNT
1790 BK
1790 BK-GU24
9" W, 15¾" H



POCKET WALL MOUNT
1797 BK
1797 BK-GU24
7" W, 12" H



1791 BK
1791 BK-GU24
11" W, 19¼" H



ITEM	BULBS	GU24 ITEM	GU24 BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1790 BK*	1-100w Med.	1790 BK-GU24*	1-26w GU24	9"	9¼"	4½" W, 12" H Back Plate	
1791 BK	3-60w Cand.	1791 BK-GU24	1-26w GU24			3" Dia. Post Fitter	
1792 BK	3-60w Cand.	1792 BK-GU24	1-26w GU24			5" Square Canopy	6', 5'
1794 BK	2-60w Cand.	1794 BK-GU24	1-26w GU24	11"	11¼"	4½" W, 12" H Back Plate	
1797 BK*	1-60w Cand.	1797 BK-GU24*	1-13w GU24	5½"	7½"	5" W, 9½" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.


MONDRIAN™

FINISH BUCKEYE BRONZE
GLASS ART GLASS PANELS


Mondrian's unique patterned glass adds a geometric panache to the durable brass and aluminum construction. These chic pocket style wall mounted lanterns are ADA compliant.

Mondrian Chandelier, pages 216-217




2154 KZ
9" W, 14¼" H




2155 KZ
7" W, 24" H




2150 KZ
7" W, 11" H


ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
2150 KZ	1-60w Cand.	4"	5½"	7" W, 10¼" H
2154 KZ	2-60w Cand.	4"	7¼"	9" W, 13¼" H
2155 KZ	3-60w Cand.	4"	12"	7" W, 23" H



“SLEEK LINES are what I usually lean towards, depending on the style of the space, and *SPECIAL GLASS* is definitely a favorite design element of mine.”

GINGER BREWTON
GINGER BREWTON INTERIORS
CHARLESTON, SC

CLAYTON™

FINISH GREYSTONE
GLASS CLEAR WATER

Clayton's transitional pocket lantern features a shallow wide roof, clear water glass and a distinctive updated Arts & Crafts design constructed from solid aluminum.



2430 GS
8¾" W, 12½" H



2434 GS
8¾" W, 18½" H



2435 GS
11" W, 16" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2430 GS	2-60w Cand.	7"	7½"	4¾" W, 8¾" H	OZ
2434 GS	2-60w Cand.	7"	10½"	4¾" W, 14¾" H	OZ
2435 GS	3-60w Cand.	9"	9¾"	4¾" W, 11" H	OZ

Clayton's transitional pocket lantern features a shallow wide roof, clear water glass and a distinctive updated Arts & Crafts design constructed from solid aluminum.

CLAYTON™

OIL RUBBED BRONZE FINISH
CLEAR WATER GLASS



2435 OZ
11" W, 16" H



2434 OZ
8¾" W, 18½" H



2430 OZ
8¾" W, 12½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	ADDITIONAL FINISHES
2430 OZ	2-60w Cand.	7"	7½"	4¾" W, 8¾" H	GS
2434 OZ	2-60w Cand.	7"	10½"	4¾" W, 14¾" H	GS
2435 OZ	3-60w Cand.	9"	9¾"	4¾" W, 11" H	GS

RANDOLPH™

FINISH AUTUMN

GLASS CLEAR SEEDY GLASS PANELS, ETCHED SEEDY GLASS PANELS

Randolph's traditional design features a bold oval pattern in die cast aluminum construction that complements a variety of exteriors.

OBJECT OF OUR *AFFECTION*

Randolph fixtures are provided with both clear and etched seedy glass panels for easy customization.






1495 AM
1495 AM-GU24
1495 AM-LED
11" W, 19½" H
(shown with etched
seedy glass)








1492 AM
1492 AM-GU24
1492 AM-LED
8" W, 14¼" H
(shown with clear
seedy glass)




1494 AM
1494 AM-GU24
1494 AM-LED
8" W, 13¾" H
(shown with clear
seedy glass)






1490 AM
1490 AM-GU24
6" W, 11" H
(shown with etched
seedy glass)





1491 AM
1491 AM-GU24
1491 AM-LED
8" W, 16¼" H
(shown with etched
seedy glass)



1499 AM
1499 AM-GU24
1499 AM-LED
11" W, 20¾" H
(shown with clear
seedy glass)





ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1490 AM*	1-75w Med.	1490 AM-GU24*	1-18w GU24			7"	2"	4½" W, 6" H Back Plate		BK
1491 AM	1-100w Med.	1491 AM-GU24	1-26w GU24	1491 AM-LED	1-15w LESM-100			3" Dia. Post Fitter		BK
1492 AM*	1-100w Med.	1492 AM-GU24*	1-26w GU24	1492 AM-LED	1-15w LESM-100			5" Square Canopy	6', 5'	BK
1494 AM*	1-100w Med.	1494 AM-GU24*	1-26w GU24	1494 AM-LED	1-15w LESM-100	9"	2¼"	5½" W, 8" H Back Plate		BK
1495 AM*	1-100w Med.	1495 AM-GU24*	1-26w GU24	1495 AM-LED	1-15w LESM-100	12"	3¼"	7" W, 11" H Back Plate		BK
1499 AM	1-100w Med.	1499 AM-GU24	1-26w GU24	1499 AM-LED	1-15w LESM-100			3" Dia. Post Fitter		BK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

RANDOLPH™

FINISH BLACK

GLASS CLEAR SEEDY GLASS PANELS, ETCHED SEEDY GLASS PANELS

Randolph's traditional design features a bold oval pattern in die cast aluminum construction that complements a variety of exteriors.



1495 BK
1495 BK-GU24
1495 BK-LED
11" W, 19½" H
(shown with etched
seedy glass)






1492 BK
1492 BK-GU24
1492 BK-LED
8" W, 14¼" H
(shown with clear seedy glass)







1494 BK
1494 BK-GU24
1494 BK-LED
8" W, 13¾" H
(shown with clear seedy glass)










1490 BK
1490 BK-GU24
6" W, 11" H
(shown with etched seedy glass)





1491 BK
1491 BK-GU24
1491 BK-LED
8" W, 16¼" H
(shown with etched seedy glass)



1499 BK
1499 BK-GU24
1499 BK-LED
11" W, 20¾" H
(shown with clear seedy glass)





ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1490 BK*	1-75w Med.	1490 BK-GU24*	1-18w GU24			7"	2"	4½" W, 6" H Back Plate		AM
1491 BK	1-100w Med.	1491 BK-GU24	1-26w GU24	1491 BK-LED	1-15w LESM-100			3" Dia. Post Fitter		AM
1492 BK*	1-100w Med.	1492 BK-GU24*	1-26w GU24	1492 BK-LED	1-15w LESM-100			5" Square Canopy	6', 5'	AM
1494 BK*	1-100w Med.	1494 BK-GU24*	1-26w GU24	1494 BK-LED	1-15w LESM-100	9"	2¼"	5½" W, 8" H Back Plate		AM
1495 BK*	1-100w Med.	1495 BK-GU24*	1-26w GU24	1495 BK-LED	1-15w LESM-100	12"	3¼"	7" W, 11" H Back Plate		AM
1499 BK	1-100w Med.	1499 BK-GU24	1-26w GU24	1499 BK-LED	1-15w LESM-100			3" Dia. Post Fitter		AM

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

ENZO™

FINISH AUTUMN
GLASS CLEAR SEEDY

Enzo is inspired by a romantic lantern design. Blending beauty and durability, the intricately die cast aluminum construction features graceful scrolls with Old World allure while the rich Autumn finish and clear seedy glass meld timeless elegance.



2275 AM
10" W, 18¾" H



2272 AM
10" W, 19" H



2278 AM
10" W, 28½" H



2274 AM
8" W, 15¼" H



2271 AM
10" W, 21" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2271 AM	1-100w Med.			3" Dia. Post Fitter	
2272 AM*	1-100w Med.			5" Square Canopy	6', 5'
2274 AM*	1-100w Med.	9½"	6"	5" W, 15" H Back Plate	
2275 AM	1-100w Med.	11½"	7"	5¼" W, 18½" H Back Plate	
2278 AM	1-100w Med.	11¾"	14½"	5¼" W, 18½" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

TAHOE™

FINISH REGENCY BRONZE

GLASS CLEAR SEEDY WATER GLASS WITH COPPER FOIL ART GLASS ACCENTS

Tahoe makes a classic Arts & Crafts design statement in cast aluminum construction with panels of clear seedy water glass and copper foil art glass accents.



2244 RB
12" W, 22½" H



2242 RB
12" W, 22½" H



2240 RB
8½" W, 17" H



2243 RB
9½" W, 6" H



2246 RB
6½" W, 12" H



2241 RB
12" W, 22¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2240 RB	3-40w Cand.	11"	9¾"	4½" W, 14" H Back Plate	
2241 RB	4-40w Cand.			3" Dia. Post Fitter	
2242 RB	4-40w Cand.			5½" Dia. Canopy	6', 5'
2243 RB	2-60w Med.				
2244 RB	4-40w Cand.	14¾"	13¼"	4½" W, 18" H Back Plate	
2246 RB	1-60w Med.	9"	7½"	4½" W, 9¼" H Back Plate	

For posts and pier mounts, see pages 748-749.

WESTWINDS™

FINISH SIENNA

GLASS CLEAR WATER GLASS PANELS

Westwinds features intricate stamped filigree detailing in a classic Sienna finish. The durable solid brass construction and clear water glass panels impart an authentic, timeless feel.



2996 SN
12³/₄" W, 27¹/₂" H



2992 SN
10½" W, 16¼" H



2995 SN
10½" W, 22½" H



2989 SN
6" W, 11¼" H



2990 SN
8½" W, 19" H



2991 SN
13" W, 20½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2989 SN*	1-60w Med.	6½"	7½"	4¾" W, 5½" H Back Plate	
2990 SN	2-40w Cand.	9½"	13½"	4½" W, 9½" H Back Plate	
2991 SN	3-40w Cand.			3" Dia. Post Fitter	
2992 SN	3-40w Cand.			5½" Dia. Canopy	6', 5'
2995 SN	3-40w Cand.	12½"	17½"	4¾" W, 9½" H Back Plate	
2996 SN	3-40w Cand.	14¼"	21½"	4½" W, 12¼" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

TRELLIS™

FINISH REGENCY BRONZE
GLASS CLEAR SEEDY



Trellis path lights are available in the Hinkley Landscape Lighting Catalog.

Trellis is a traditional European hanging wall lantern design featuring a solid aluminum construction in a Regency Bronze finish with dense clear seedy glass. The large scroll arm detail, cast loop finial and true rivet detail create a refined elegance.



1435 RB
1435 RB-LED
11" W, 22¼" H





1429 RB
1429 RB-LED
9" W, 14¾" H
(can be used with 1433RB-SCR)
T24



1433 RB
1433 RB-LED
(1433RB-SCR included)
29¾" W, 14¾" H
T24



1433 RB-SCR
29¾" W, 9" H



THE SUGGESTION BOX Optional scrolls allow for a variety of decorative arrangements.



1438 RB
1438 RB-LED
13" W, 26¼" H
T24



PIER MOUNT
1437 RB
1437 RB-LED
11" W, 19¾" H
T24



1431 RB
1431 RB-LED
11" W, 21" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY
1429 RB	3-60w Cand.	1429 RB-LED	1-15w LESM-100	11½"	8½"	4½" W, 10" H Back Plate
1431 RB	3-60w Cand.	1431 RB-LED	1-15w UNI-100			3" Dia. Post Fitter
1433 RB	3-60w Cand.	1433 RB-LED	1-15w UNI-100	11½"	8½"	4½" W, 10" H Back Plate
1433 RB-SCR						
1435 RB	4-60w Cand.	1435 RB-LED	1-15w UNI-100	16½"	8"	4½" W, 10" H Back Plate
1437 RB	4-60w Cand.	1437 RB-LED	1-15w LESM-100			10¼" Square Base
1438 RB	4-60w Cand.	1438 RB-LED	1-15w UNI-100	19"	9½"	5" W, 13" H Back Plate

For posts and pier mounts, see pages 748-749.



1432 RB
1432 RB-LED
11" W, 23¼" H
T24



1434 RB
1434 RB-LED
9" W, 19¾" H
T24



1439 RB
16" W, 52" H



1430 RB
1430 RB-LED
7" W, 15¼" H
T24



1436 RB
11" W, 35¾" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1430 RB*	1-100w Med.	1430 RB-LED	1-15w UNI-100	11¼"	6"	4½" W, 7" H Back Plate	
1432 RB	3-60w Cand.	1432 RB-LED	1-15w UNI-100			4½" Square Canopy	6', 5'
1434 RB	3-60w Cand.	1434 RB-LED	1-15w UNI-100	14½"	8"	4½" W, 10" H Back Plate	
1436 RB	4-60w Cand.			16½"	18¾"	4½" W, 13" H Back Plate	
1439 RB	4-60w Cand.			24"	27½"	4¾" W, 20" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7.

“I love exterior lighting that
ILLUMINATES PATHWAYS AND TREES,
allowing you to see the depth
and space of the exterior.”

KATIE LYDON | KATIE LYDON INTERIORS
NEW YORK, NY



SORRENTO™

FINISH AGED IRON

GLASS CLEAR SEEDY (OUTER GLASS), OPTIC ETCHED AMBER (INNER GLASS)

Sorrento's cast aluminum construction and flourishing cast details are enhanced by its hand-applied Aged Iron finish with copper highlights. Stunning optic etched amber inner glass is surrounded by panels of clear seedy outer glass, creating a grand statement.

Sorrento Chandelier, page 188



1425 AI
12¼" W, 26¾" H



1422 AI
12¼" W, 24" H



1424 AI
9¾" W, 20½" H



1420 AI
8" W, 17" H



1421 AI
12¼" W, 28¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE	WIRE/ CHAIN
1420 AI	1-100w Med.	11½"	10"	5" W, 9" H Back Plate	
1421 AI	1-100w Med.			3" Dia. Post Fitter	
1422 AI	1-100w Med.			5½" Dia. Canopy	6', 5'
1424 AI	1-100w Med.	13½"	12"	5" W, 9" H Back Plate	
1425 AI	1-100w Med.	16½"	16½"	5" W, 13" H Back Plate	

For posts and pier mounts, see pages 748-749.

CASA™

FINISH OLDE BLACK
GLASS LIGHT ETCHED AMBER

Casa features solid aluminum construction with twisted wrought iron details and hand-forged scrollwork in an Olde Black finish to complete its rustic-chic appeal with a Southwestern flair.

Casa Chandelier, pages 102-105

Casa Bath, page 509



1145 OL
1145 OL-GU24
1145 OL-LED
11¾" W, 20¾" H








1142 OL
1142 OL-GU24
1142 OL-LED
11 3/4" DIA., 18 1/2" H







1144 OL
1144 OL-GU24
1144 OL-LED
9 3/4" W, 17 1/4" H



1140 OL
1140 OL-GU24
1140 OL-LED
7" W, 13" H







1141 OL
1141 OL-GU24
1141 OL-LED
11 3/4" DIA., 24" H





ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1140 OL*	1-60w Med.	1140 OL-GU24*	1-13w GU24	1140 OL-LED	1-15w LESM-100	8"	6 3/4"	4 1/2" W, 7" H Back Plate	
1141 OL	3-60w Cand.	1141 OL-GU24	1-26w GU24	1141 OL-LED	1-15w LESM-100			3" Dia. Post Fitter	
1142 OL*	1-100w Med.	1142 OL-GU24*	1-26w GU24	1142 OL-LED	1-15w LESM-100			5 1/4" Dia. Canopy	6', 5'
1144 OL*	1-75w Med.	1144 OL-GU24*	1-18w GU24	1144 OL-LED	1-15w LESM-100	9 1/4"	9 1/2"	4 1/2" W, 9" H Back Plate	
1145 OL*	1-100w Med.	1145 OL-GU24*	1-26w GU24	1145 OL-LED	1-15w LESM-100	11 1/4"	10 3/4"	4 1/2" W, 9" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

BRYNMAR™

FINISH REGENCY BRONZE
GLASS AMBER LINEN




Gorgeous details add drama to Brynmar's classic cast aluminum design. The decorative cast leaf and cross-hatch detailing in a Regency Bronze finish complement the stylish amber linen glass.






1935 RB
1935 RB-GU24
1935 RB-LED
12" W, 27½" H







1932 RB
1932 RB-GU24
1932 RB-LED
12" W, 27¾" H









1934 RB
1934 RB-GU24
1934 RB-LED
9½" W, 20¼" H









1936 RB
1936 RB-GU24
1936 RB-LED
5" W, 8¾" H






1930 RB
1930 RB-GU24
1930 RB-LED
7" W, 12¼" H






1931 RB
1931 RB-GU24
1931 RB-LED
12" W, 27" H
(shown as pier mount with 1304 RB)*




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1930 RB**	1-60w Med.	1930 RB-GU24**	1-26w GU24	1930 RB-LED	1-15w LESM-100	8"	4"	4¾" W, 7" H Back Plate	
1931 RB	1-100w Med.	1931 RB-GU24	1-26w GU24	1931 RB-LED	1-15w LESM-100			3" Dia. Post Fitter	
1932 RB**	1-100w Med.	1932 RB-GU24**	1-26w GU24	1932 RB-LED	1-15w LESM-100			5½" Dia. Canopy	6', 5'
1934 RB**	1-75w Med.	1934 RB-GU24**	1-26w GU24	1934 RB-LED	1-15w LESM-100	10½"	10¾"	5" W, 14" H Back Plate	
1935 RB**	1-100w Med.	1935 RB-GU24**	1-26w GU24	1935 RB-LED	1-15w LESM-100	12¾"	14"	5" W, 18" H Back Plate	
1936 RB**	1-60w Med.	1936 RB-GU24**	1-26w GU24	1936 RB-LED	1-15w LESM-100	6"	3¼"	4¾" W, 6" H Back Plate	

*Not for use within 4 ft. of ground. **When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

PLANTATION™

FINISH PEARL BRONZE
GLASS INSIDE ETCHED AMBER OPTIC



Plantation path lights are available in the Hinkley Landscape Lighting Catalog.

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped optic glass, durable brass and aluminum construction and elaborate, decorative cast detailing to create a noble statement.

Plantation Chandelier, pages 140-147
Plantation Bath, pages 514-515



2124 PZ
2124 PZ-GU24
2124 PZ-LED
10¼" W, 28" H









2122 PZ
2122 PZ-GU24
2122 PZ-LED
12½" DIA., 28½" H







2128 PZ
2128 PZ-GU24
12" DIA., 8" H







2123 PZ
2123 PZ-GU24
2123 PZ-LED
16" DIA., 8¾" H









2126 PZ
2126 PZ-GU24
2126 PZ-LED
6" W, 14" H






2120 PZ
2120 PZ-GU24
2120 PZ-LED
8" W, 21¼" H






2121 PZ
2121 PZ-GU24
2121 PZ-LED
10¼" DIA., 25¼" H




ITEM	BULBS	GU24 ITEM	GU24 BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2120 PZ	1-75w Med.	2120 PZ-GU24	1-18w GU24	2120 PZ-LED	1-15w LESM-100	11"	11½"	5" W, 16" H Back Plate	
2121 PZ	1-100w Med.	2121 PZ-GU24	1-26w GU24	2121 PZ-LED	1-15w LESM-100			3" Dia. Post Fitter	
2122 PZ	1-100w Med.	2122 PZ-GU24	1-26w GU24	2122 PZ-LED	1-15w LESM-100			6" Dia. Canopy	6', 5'
2123 PZ	3-60w Med.	2123 PZ-GU24	3-13w GU24	2123 PZ-LED	1-32w FSI-200				
2124 PZ	1-75w Med.	2124 PZ-GU24	1-18w GU24	2124 PZ-LED	1-15w LESM-100	13½"	14½"	5" W, 20" H Back Plate	
2126 PZ	1-60w Med.	2126 PZ-GU24	1-13w GU24	2126 PZ-LED	1-15w LESM-100	7"	5"	4½" W, 8" H Back Plate	
2128 PZ	3-60w Med.	2128 PZ-GU24	2-13w GU24						

For posts and pier mounts, see pages 748-749.

PLANTATION™

FINISH COPPER BRONZE
GLASS CLEAR OPTIC



Plantation path lights are available in the Hinkley Landscape Lighting Catalog.

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped optic glass, durable brass and aluminum construction and elaborate, decorative cast detailing to create a noble statement.

Plantation Chandelier, pages 140-147
Plantation Bath, pages 514-515



2225 CB
12½" W, 34" H



2222 CB
12½" DIA., 28½" H



4102 CB
12" DIA., 8" H



2224 CB
10¼" W, 28" H



4881 CB
16" DIA., 8¾" H



2226 CB
6" W, 14" H



2220 CB
8" W, 22" H



2221 CB
10¼" DIA., 25¼" H
(shown as pier mount with 1304 CB)*



2227 CB
12½" DIA., 29½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2220 CB	1-75w Med.	11"	11½"	5" W, 16" H Back Plate	
2221 CB	3-40w Cand.			3" Dia. Post Fitter	
2222 CB	4-40w Cand.			6" Dia. Canopy	6', 5'
2224 CB	3-40w Cand.	13½"	14½"	5" W, 20" H Back Plate	
2225 CB	4-40w Cand.	17½"	17½"	5" W, 24" H Back Plate	
2226 CB	1-60w Med.	7"	5"	4¾" W, 8" H Back Plate	
2227 CB	4-40w Cand.			3" Dia. Post Fitter	
4102 CB	2-60w Med.				
4881 CB	3-60w Med.				

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 748-749.

RALEY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR WATER GLASS PANELS



Raley path lights are available in the Hinkley Landscape Lighting Catalog.

Raley's regal appearance features cast aluminum construction, a bold Oil Rubbed Bronze finish, flourishing details and clear water glass panels for a dignified style statement.



1609 OZ
13" W, 41¼" H



1602 OZ
11¾" DIA., 27½" H



1605 OZ
11¾" W, 31¼" H



1600 OZ
7¼" W, 16½" H



1604 OZ
9½" W, 25½" H



1601 OZ
11¾" DIA., 26¼" H
(shown as pier mount with 1304 OZ)*

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1600 OZ**	1-60w Med.	9½"	10½"	4½" W, 7½" H Back Plate		MB
1601 OZ	4-40w Cand.			3" Dia. Post Fitter		MB
1602 OZ	4-40w Cand.			5½" Dia. Canopy	6', 5'	MB
1604 OZ	3-40w Cand.	12¼"	14"	4½" W, 9½" H Back Plate		MB
1605 OZ	4-40w Cand.	14¾"	16¼"	4½" W, 9½" H Back Plate		MB
1609 OZ	4-40w Cand.	17½"	23¾"	5½" W, 18" H Back Plate		MB

*Not for use within 4 ft. of ground.**When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

RALEY™

FINISH MUSEUM BLACK
GLASS CLEAR WATER GLASS PANELS



Raley path lights are available in the Hinkley Landscape Lighting Catalog.

Raley's regal appearance features cast aluminum construction, a bold Museum Black finish, flourishing details and clear water glass panels for a dignified style statement.



1609 MB
13" W, 41¼" H



1602 MB
11¾" DIA., 27½" H



1605 MB
11¾" W, 31¼" H



1600 MB
7¼" W, 16½" H



1604 MB
9½" W, 25½" H



1601 MB
11¾" DIA., 26¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1600 MB*	1-60w Med.	9½"	10½"	4½" W, 7½" H Back Plate		OZ
1601 MB	4-40w Cand.			3" Dia. Post Fitter		OZ
1602 MB	4-40w Cand.			5½" Dia. Canopy	6', 5'	OZ
1604 MB	3-40w Cand.	12¼"	14"	4½" W, 9½" H Back Plate		OZ
1605 MB	4-40w Cand.	14¾"	16¼"	4½" W, 9½" H Back Plate		OZ
1609 MB	4-40w Cand.	17½"	23¾"	5½" W, 18" H Back Plate		OZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

WINDSOR™

FINISH RIVER ROCK
GLASS CLEAR WATER GLASS

Windsor combines elegant details and decorative cast detailing into its cast aluminum construction. The unique River Rock finish and clear water glass add to its majestic style.



1929 RK
1929 RK-LED
14" W, 42" H





1892 RK
1892 RK-LED
12½" DIA., 28½" H
T24



1895 RK
1895 RK-LED
12½" W, 32" H
T24



1894 RK
1894 RK-LED
9½" W, 25½" H
T24



1890 RK
1890 RK-LED
7" W, 12½" H
T24



1898 RK
1898 RK-LED
9½" W, 20¾" H
T24



1899 RK
1899 RK-LED
12½" W, 25¾" H
T24



1891 RK
1891 RK-LED
12½" DIA., 30" H
T24



1921 RK
1921 RK-LED
14¼" DIA., 34¾" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1890 RK*	1-75w Med.	1890 RK-LED	1-15w LESM-100	8¼"	4¾"	5¾" W, 8" H Back Plate		BK
1891 RK	4-40w Cand.	1891 RK-LED	1-15w LESM-100			3" Dia. Post Fitter		BK
1892 RK	4-40w Cand.	1892 RK-LED	1-15w LESM-100			5½" Dia. Canopy	6', 5'	BK
1894 RK	3-40w Cand.	1894 RK-LED	1-15w LESM-100	12"	13"	5¾" W, 12" H Back Plate		BK
1895 RK	4-40w Cand.	1895 RK-LED	1-15w LESM-100	15½"	16½"	6¼" W, 15" H Back Plate		BK
1898 RK	3-40w Cand.	1898 RK-LED	1-15w LESM-100	11¾"	12½"	5¾" W, 12" H Back Plate		BK
1899 RK	4-40w Cand.	1899 RK-LED	1-15w UNI-100	15½"	15¼"	6¼" W, 15" H Back Plate		BK
1921 RK	6-40w Cand.	1921 RK-LED	2-15w LESM-100			3" Dia. Post Fitter		BK
1929 RK	6-40w Cand.	1929 RK-LED	2-15w LESM-100	17"	19½"	6¼" W, 17" H Back Plate		BK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

WINDSOR™

FINISH BLACK

GLASS CLEAR WATER GLASS

Windsor combines elegant details and decorative cast detailing into its cast aluminum construction. The Black finish and clear water glass add to its majestic style.



1929 BK
1929 BK-LED
14" W, 42" H





1892 BK
1892 BK-LED
12½" DIA., 28½" H



1895 BK
1895 BK-LED
12½" W, 32" H



1894 BK
1894 BK-LED
9½" W, 25½" H



1890 BK
1890 BK-LED
7" W, 12½" H



1898 BK
1898 BK-LED
9½" W, 20¾" H



1899 BK
1899 BK-LED
12½" W, 25¾" H



1891 BK
1891 BK-LED
12½" DIA., 30" H



1921 BK
1921 BK-LED
14¼" DIA., 34¾" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1890 BK*	1-75w Med.	1890 BK-LED	1-15w LESM-100	8¼"	4¾"	5¾" W, 8" H Back Plate		RK
1891 BK	4-40w Cand.	1891 BK-LED	1-15w LESM-100			3" Dia. Post Fitter		RK
1892 BK	4-40w Cand.	1892 BK-LED	1-15w LESM-100			5½" Dia. Canopy	6', 5'	RK
1894 BK	3-40w Cand.	1894 BK-LED	1-15w LESM-100	12"	13"	5¾" W, 12" H Back Plate		RK
1895 BK	4-40w Cand.	1895 BK-LED	1-15w LESM-100	15½"	16½"	6¼" W, 15" H Back Plate		RK
1898 BK	3-40w Cand.	1898 BK-LED	1-15w LESM-100	11¾"	12½"	5¾" W, 12" H Back Plate		RK
1899 BK	4-40w Cand.	1899 BK-LED	1-15w UNI-100	15½"	15¼"	6¼" W, 15" H Back Plate		RK
1921 BK	6-40w Cand.	1921 BK-LED	2-15w LESM-100			3" Dia. Post Fitter		RK
1929 BK	6-40w Cand.	1929 BK-LED	2-15w LESM-100	17"	19½"	6¼" W, 17" H Back Plate		RK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

FORUM™

FINISH MUSEUM BLACK
GLASS SEEDY WATER GLASS

Forum's distinguished silhouette features cast aluminum construction in a Museum Black finish with decorative cast detailing and generous panels of seedy water glass.



1940 MB
7" W, 21" H



1944 MB
9½" W, 27½" H



1942 MB
9½" W, 25¾" H



1941 MB
9½" W, 23½" H



1946 MB
5½" W, 12¾" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1940 MB	1-75w Med.	9¾"	9½"	5" W, 8" H Back Plate		FZ
1941 MB	3-40w Cand.			3" Dia. Post Fitter		FZ
1942 MB	3-40w Cand.			5½" Dia. Canopy	6', 5'	FZ
1944 MB	3-40w Cand.	12"	11"	5" W, 8" H Back Plate		FZ
1946 MB*	1-40w Med.	7½"	6"	4¾" W, 6½" H Back Plate		FZ

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Forum's distinguished silhouette features cast aluminum construction in a French Bronze finish with decorative cast detailing and generous panels of seedy water glass.

FORUM™

FRENCH BRONZE FINISH
SEEDY WATER GLASS GLASS



1942 FZ
9½" W, 25¾" H



1944 FZ
9½" W, 27½" H



1940 FZ
7" W, 21" H



1946 FZ
5½" W, 12¾" H



1941 FZ
9½" W, 23½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1940 FZ	1-75w Med.	9¾"	9½"	5" W, 8" H Back Plate		MB
1941 FZ	3-40w Cand.			3" Dia. Post Fitter		MB
1942 FZ	3-40w Cand.			5½" Dia. Canopy	6', 5'	MB
1944 FZ	3-40w Cand.	12"	11"	5" W, 8" H Back Plate		MB
1946 FZ*	1-40w Med.	7½"	6"	4¾" W, 6½" H Back Plate		MB

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

KEY WEST™

FINISH REGENCY BRONZE
GLASS CLEAR SEEDY

Key West captures a gracious elegance featuring cast aluminum construction and ornate decorative cast detailing in a Regency Bronze finish, complemented by clear seedy glass.



2905 RB
12" W, 27" H



2902 RB
12" DIA., 23¾" H



2904 RB
9" W, 21" H



2903 RB
15" DIA., 8¼" H



2900 RB
7" W, 16¼" H



2901 RB
12" DIA., 21¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2900 RB	1-60w Med.	9¼"	8¾"	4½" W, 7" H Back Plate	
2901 RB	3-60w Cand.			3" Dia. Post Fitter	
2902 RB	3-60w Cand.			5½" Dia. Canopy	6, 5'
2904 RB	1-75w Med.	12¼"	12½"	4½" W, 9" H Back Plate	
2905 RB	3-60w Cand.	14¾"	13¾"	4½" W, 9" H Back Plate	

For posts and pier mounts, see pages 748-749.

REGAL™

FINISH BLACK GRANITE
GLASS CLEAR SEEDY WATER GLASS

Regal has a grand Old World style that features cast aluminum construction and elegant decorative stamped detailing in a Black Granite finish. Clear seedy water glass adds timeless sophistication.



1726 BG
12" W, 32¼" H



1722 BG
8¼" W, 18" H



1720 BG
6½" W, 13" H



1713 BG
11¾" W, 9" H



1725 BG
8½" W, 23½" H



1721 BG
8½" W, 22½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1713 BG	4-40w Cand.				
1720 BG	2-40w Cand.	8¼"	4¾"	4½" W, 9" H Back Plate	
1721 BG	3-40w Cand.			3" Dia. Post Fitter	
1722 BG	3-40w Cand.			5" Dia. Canopy	6', 5'
1725 BG	3-40w Cand.	11¼"	7¼"	5" W, 14" H Back Plate	
1726 BG	4-40w Cand.	14¼"	10"	5" W, 18½" H Back Plate	

For posts and pier mounts, see pages 748-749.

TRAFALGAR™

FINISH MOCHA
GLASS CLEAR SEEDY

Trafalgar's grand design in sturdy cast aluminum adds historical flair with delicate scroll arch detail, authentic distressed finish and clear seedy glass.



1319 MO
1319 MO-GU24
12" W, 26½" H

1315 MO
1315 MO-GU24
10" W, 22" H

1312 MO
1312 MO-GU24
12" W, 24¾" H

1311 MO
1311 MO-GU24
12" W, 27½" H

1314 MO
1314 MO-GU24
8" W, 17½" H

1316 MO
1316 MO-GU24
6" W, 10" H

ITEM	BULBS	GU24 ITEM	GU24 BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1311 MO	3-40w Cand.	1311 MO-GU24	1-26w GU24			3" Dia. Post Fitter		MB
1312 MO	3-40w Cand.	1312 MO-GU24	1-26w GU24			5" Dia. Canopy	6', 5'	MB
1314 MO	1-75w Med.	1314 MO-GU24	1-18w GU24	10½"	7½"	6" W, 12" H Back Plate		MB
1315 MO	3-40w Cand.	1315 MO-GU24	1-18w GU24	13½"	9½"	7¼" W, 14¼" H Back Plate		MB
1316 MO*	1-60w Med.	1316 MO-GU24	1-13w GU24	7½"	5¼"	4½" W, 7" H Back Plate		MB
1319 MO	3-40w Cand.	1319 MO-GU24	1-26w GU24	16"	11¼"	7¼" W, 17¼" H Back Plate		MB

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Trafalgar's grand design in sturdy cast aluminum adds historical flair with delicate scroll arch detail, authentic distressed finish and clear seeded glass.

TRAFALGAR™

MUSEUM BLACK FINISH
CLEAR SEEDY GLASS



ITEM	BULBS	GU24 ITEM	GU24 BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1311 MB	3-40w Cand.	1311 MO-GU24	1-26w GU24			3" Dia. Post Fitter		MO
1312 MB	3-40w Cand.	1312 MO-GU24	1-26w GU24			5" Dia. Canopy	6', 5'	MO
1314 MB	1-75w Med.	1314 MO-GU24	1-18w GU24	10½"	7½"	6" W, 12" H Back Plate		MO
1315 MB	3-40w Cand.	1315 MO-GU24	1-18w GU24	13½"	9½"	7¼" W, 14¼" H Back Plate		MO
1316 MB*	1-60w Med.	1316 MO-GU24	1-13w GU24	7½"	5¼"	4½" W, 7" H Back Plate		MO
1319 MB	3-40w Cand.	1319 MO-GU24	1-26w GU24	16"	11¼"	7¼" W, 17¼" H Back Plate		MO

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

WABASH™

FINISH MOCHA

GLASS CLEAR BEVELED WITH ETCHED GLASS CORNER PANELS

Wabash features solid aluminum construction with clear beveled glass, etched glass corner panels and decorative chevron detailing in a distressed finish.



1336 MO
1336 MO-LED
6¼" W, 10½" H




1334 MO
1334 MO-LED
8¼" W, 13¾" H




1332 MO
1332 MO-LED
11" W, 17¾" H




1331 MO
1331 MO-LED
11" W, 23" H




1335 MO
1335 MO-LED
11" W, 18½" H


ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1331 MO	3-40w Cand.	1331 MO-LED	1-15w LESM-100			3" Dia. Post Fitter		MB
1332 MO	3-40w Cand.	1332 MO-LED	1-15w UNI-100			4½" Dia. Canopy	6', 5'	MB
1334 MO	2-40w Cand.	1334 MO-LED	1-10w UNI-60	10"	4¼"	6" W, 9" H Back Plate		MB
1335 MO	3-40w Cand.	1335 MO-LED	1-15w UNI-100	13¾"	5¼"	5½" W, 11¾" H Back Plate		MB
1336 MO*	1-60w Med.	1336 MO-LED	1-10w UNI-60	7¾"	3½"	4½" W, 6¾" H Back Plate		MB

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

Wabash features solid aluminum construction with clear beveled glass, etched glass corner panels and decorative chevron detailing in a distressed finish.

WABASH™

MUSEUM BLACK FINISH
CLEAR BEVELED WITH ETCHED GLASS CORNER PANELS GLASS



1332 MB
1332 MB-LED
11" W, 17¾" H
T24



1334 MB
1334 MB-LED
8¼" W, 13¾" H
T24



1336 MB
1336 MB-LED
6¼" W, 10½" H
T24



1335 MB
1335 MB-LED
11" W, 18½" H
T24



1331 MB
1331 MB-LED
11" W, 23" H
T24

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	ADDITIONAL FINISHES
1331 MB	3-40w Cand.	1331 MB-LED	1-15w LESM-100			3" Dia. Post Fitter		MO
1332 MB	3-40w Cand.	1332 MB-LED	1-15w UNI-100			4½" Dia. Canopy	6', 5'	MO
1334 MB	2-40w Cand.	1334 MB-LED	1-10w UNI-60	10"	4¼"	6" W, 9" H Back Plate		MO
1335 MB	3-40w Cand.	1335 MB-LED	1-15w UNI-100	13¾"	5¼"	5½" W, 11¾" H Back Plate		MO
1336 MB*	1-60w Med.	1336 MB-LED	1-10w UNI-60	7¾"	3½"	4½" W, 6¾" H Back Plate		MO

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

OXFORD™

FINISH MIDNIGHT BRONZE
GLASS CLEAR OPTIC

Oxford's sophisticated silhouette features solid aluminum construction with bead detailing in a Midnight Bronze finish, complemented by clear optic glass for a chic yet classic style statement.



1245 MN
12" W, 28½" H



1242 MN
12" DIA., 27½" H



1240 MN
7" W, 17¼" H



1243 MN
16¼" DIA., 7½" H



1244 MN
9¾" W, 23½" H



1241 MN
12" DIA., 28¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1240 MN	1-60w Med.	9"	10"	4¾" W, 9" H Back Plate	
1241 MN	3-40w Cand.			3" Dia. Post Fitter	
1242 MN	3-40w Cand.			6¾" Dia. Canopy	6', 5'
1243 MN	2-60w Med.				
1244 MN	3-40w Cand.	12¼"	12"	4¾" W, 9" H Back Plate	
1245 MN	3-40w Cand.	15"	16"	4¾" W, 16" H Back Plate	

For posts and pier mounts, see pages 748-749.

CAMELOT™

FINISH BLACK

GLASS CLEAR BEVELED PANELS

Camelot's stunning clear beveled glass panels add a regal elegance to this traditional cast aluminum design in a rich Black finish.



1705 BK
12" W, 35" H



1702 BK
12" W, 25" H



1704 BK
8½" W, 26¾" H



1700 BK
6½" W, 13¼" H



1707 BK
12" W, 25½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1700 BK*	1-75w Med.	7½"	10½"	4½" W, 7½" H Back Plate	
1702 BK	3-40w Cand.			5" Dia. Canopy	6', 5'
1704 BK	3-40w Cand.	10"	17¼"	4½" W, 9" H Back Plate	
1705 BK	3-40w Cand.	14¼"	22½"	5¼" W, 14" H Back Plate	
1707 BK	3-40w Cand.			3" Dia. Post Fitter	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

MANOR HOUSE™

FINISH BLACK
GLASS CLEAR BEVELED PANELS

Manor House is a classic lantern design featuring durable cast aluminum, clear beveled glass panels and a bold Black finish. Select-A-Lite options come standard with both candelabra and medium based sockets.



1819 BK
7" W, 12" H



1445 BK
36" W, 21" H



1471 BK
14" W, 27" H



1441 BK
11" W, 22" H



1412 BK
9" W, 15" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1412 BK	1-60w Med.			5½" Dia. Canopy	6', 5'
1441 BK	3-25w Cand. & 1-75w Med.			3" Dia. Post Fitter	
1445 BK	3-25w Cand. & 1-75w Med.	12"	14"	5" W, 8¼" H Back Plate	
1471 BK	3-40w Cand. & 1-100w Med.			3" Dia. Post Fitter	
1819 BK	1-60w Med.	12"	8"	4½" W, 5¾" H Back Plate	

For posts and pier mounts, see pages 748-749.

Manor House is a classic lantern design featuring durable cast aluminum, clear beveled glass panels and a bold Black finish. Select-A-Lite options come standard with both candelabra and medium based sockets.

MANOR HOUSE™

BLACK FINISH
CLEAR BEVELED PANELS GLASS



ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
1410 BK	3-25w Cand. & 1-60w Med.	11"	13"	4½" W, 6¾" H
1419 BK	1-60w Med.	11"	13"	4½" W, 6¾" H
1440 BK	3-25w Cand. & 1-75w Med.	12"	14"	5" W, 8¼" H
1449 BK	3-25w Cand. & 1-75w Med.	12"	14"	5" W, 8¼" H
1470 BK	3-40w Cand. & 1-100w Med.	16"	18"	5" W, 8¼" H

For posts and pier mounts, see pages 748-749.

CHESTERFIELD™

FINISH BLACK
GLASS CLEAR BEVELED PANELS

Chesterfield's clean lines and seamless transitions contribute a current design element to its traditional form. Its updated scroll arm is made from laser cut aluminum, complemented by candelabra lamping, clear seeded glass and Black powder coat finish.



1380 BK
6½" W, 17¼" H



1385 BK
10½" W, 23½" H



1382 BK
10½" DIA., 20½" H



1381 BK
10½" DIA., 23¾" H
(shown as pier mount with 1304 BK)*



1384 BK
8½" W, 20" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1380 BK	1-100w Med.	8½"	11"	4½" W, 7¼" H Back Plate	
1381 BK	3-60w Cand.			3" Dia. Post Fitter	
1382 BK	3-60w Cand.			6½" Dia. Canopy	6', 5'
1384 BK	2-60w Cand.	10½"	11¼"	4½" W, 7¼" H Back Plate	
1385 BK	3-60w Cand.	12¾"	12"	4½" W, 7¼" H Back Plate	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 748-749.

SENATOR™

Senator's stately cast aluminum and brass design features a striking Black finish with crisp panels of beveled, bound glass.

BLACK FINISH
BOUND AND BEVELED GLASS



2502 BK
13" W, 25½" H



2505 BK
13" W, 26" H



2500 BK
8½" W, 14" H



2504 BK
11" W, 21¾" H



2501 BK
13" DIA., 26½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2500 BK*	1-60w Med.	9"	6½"	5" W, 6¾" H Back Plate	
2501 BK	3-40w Cand.			3" Dia. Post Fitter	
2502 BK	3-40w Cand.			5" Dia. Canopy	6', 5'
2504 BK	3-40w Cand.	11½"	7¾"	5" W, 8¾" H Back Plate	
2505 BK	3-40w Cand.	15"	10"	6½" W, 8¾" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

EDGEWATER™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY PANELS

Edgewater's classic design features durable cast aluminum and brass construction in a rich Oil Rubbed Bronze finish with clear seedy glass.



1675 OZ
1675 OZ-LED
16" W, 25½" H





1672 OZ
10" DIA., 18½" H



1683 OZ
13" DIA., 9" H



1676 OZ
1676 OZ-LED
10" W, 17½" H



1674 OZ
1674 OZ-LED
6½" W, 11" H



1670 OZ
10" W, 21" H



1671 OZ
10" DIA., 20½" H



1677 OZ
16" DIA., 27" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1670 OZ	3-40w Cand.			9½"	14½"	5" W, 14" H Back Plate		BK
1671 OZ	3-40w Cand.					3" Dia. Post Fitter		BK
1672 OZ	3-40w Cand.					5" Dia. Canopy	6', 5'	BK
1674 OZ*	1-60w Med.	1674 OZ-LED	1-10w UNI-60	6½"	5½"	5" W, 7" H Back Plate		BK
1675 OZ	4-40w Cand.	1675 OZ-LED	1-15w UNI-100	14½"	11"	5" W, 14" H Back Plate		BK
1676 OZ	3-40w Cand.	1676 OZ-LED	1-15w UNI-100	9½"	6½"	4½" W, 9" H Back Plate		BK
1677 OZ	4-40w Cand.					3" Dia. Post Fitter		BK
1683 OZ	2-60w Med.							BK

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

EDGEWATER™

FINISH BLACK
GLASS CLEAR SEEDY PANELS

Edgewater's classic design features durable cast aluminum and brass construction in a rich Black finish with clear seedy glass.



1675 BK
1675 BK-LED
16" W, 25½" H





1672 BK
10" DIA., 18½" H





1683 BK
13" DIA., 9" H



1676 BK
1676 BK-LED
10" W, 17½" H
 



1674 BK
1674 BK-LED
6½" W, 11" H
 



1670 BK
10" W, 21" H



1671 BK
10" DIA., 20½" H



1677 BK
16" DIA., 27" H
(shown as pier mount with 1304 BK)*

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
1670 BK	3-40w Cand.			9½"	14½"	5" W, 14" H Back Plate		OZ
1671 BK	3-40w Cand.					3" Dia. Post Fitter		OZ
1672 BK	3-40w Cand.					5" Dia. Canopy	6', 5'	OZ
1674 BK**	1-60w Med.	1674 BK-LED	1-10w UNI-60	6½"	5½"	5" W, 7" H Back Plate		OZ
1675 BK	4-40w Cand.	1675 BK-LED	1-15w UNI-100	14½"	11"	5" W, 14" H Back Plate		OZ
1676 BK	3-40w Cand.	1676 BK-LED	1-15w UNI-100	9½"	6½"	4½" W, 9" H Back Plate		OZ
1677 BK	4-40w Cand.					3" Dia. Post Fitter		OZ
1683 BK	2-60w Med.							OZ

*Not for use within 4 ft. of ground. **When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

SAN CLEMENTE™

FINISH COPPER BRONZE

GLASS CLEAR BENT, BEVELED AND BOUND PANELS

San Clemente's elegant shape takes center stage with clear bent, beveled and bound glass as the central design element. Cast aluminum and brass construction complemented by exquisite cast ornamental detailing completes its captivating appeal.



2446 CB
18" W, 25¾" H



2442 CB
14" DIA., 20" H



2443 CB
15¾" DIA., 9" H



2440 CB
9½" W, 14½" H



2445 CB
14" W, 21½" H



2444 CB
12" W, 21" H



2441 CB
14" DIA., 23" H
(shown as
pier mount with
1304 CB)*



2447 CB
15½" DIA., 26½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2440 CB**	1-60w Med.	9½"	5½"	4½" W, 6½" H Back Plate		MB
2441 CB	3-40w Cand.			3" Dia. Post Fitter		MB
2442 CB	3-40w Cand.			5" Dia. Canopy	6', 5'	MB
2443 CB	2-60w Med.					MB
2444 CB	3-40w Cand.	12½"	6½"	4½" W, 9" H Back Plate		MB
2445 CB	3-40w Cand.	13"	6"	4½" W, 9" H Back Plate		MB
2446 CB	4-40w Cand.	16"	8¼"	5" W, 14" H Back Plate		MB
2447 CB	3-40w Cand.			3" Dia. Post Fitter		MB

*Not for use within 4 ft. of ground.**When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

SAN CLEMENTE™

FINISH MUSEUM BLACK

GLASS CLEAR BENT, BEVELED AND BOUND PANELS

San Clemente's elegant shape takes center stage with clear bent, beveled and bound glass as the central design element. Cast aluminum and brass construction complemented by exquisite cast ornamental detailing completes its captivating appeal.



2446 MB
18" W, 25 $\frac{3}{4}$ " H



2442 MB
14" DIA., 20" H



2444 MB
12" W, 21" H



2443 MB
15 3/4" DIA., 9" H



2440 MB
9 1/2" W, 14 1/2" H



2441 MB
14" DIA., 23" H



2447 MB
15 1/2" DIA., 26 1/2" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2440 MB*	1-60w Med.	9 1/2"	5 1/2"	4 1/2" W, 6 1/2" H Back Plate		CB
2441 MB	3-40w Cand.			3" Dia. Post Fitter		CB
2442 MB	3-40w Cand.			5" Dia. Canopy	6', 5'	CB
2443 MB	2-60w Med.					CB
2444 MB	3-40w Cand.	12 1/2"	6 1/2"	4 1/2" W, 9" H Back Plate		CB
2446 MB	4-40w Cand.	16"	8 1/4"	5" W, 14" H Back Plate		CB
2447 MB	3-40w Cand.			3" Dia. Post Fitter		CB

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.



“WE GAIN EXTRA SQUARE FOOTAGE WITH MINIMAL
EFFORT ADDING A LIVING SPACE OUTDOORS.
*Sofas and chairs, rugs, a fireplace, blankets and pillows,
bar carts...we are creating exceptional spaces!*”

SARAH SWANSON | SARAH SWANSON DESIGN
CALGARY, ALBERTA

Barrington's chic, classic style transforms this design into a modern interpretation of the traditional outdoor lantern, constructed of solid aluminum. The cast finials combine with the clear seedy glass for added authenticity, while the lustrous finish is created in a multi-step, hand-painted process.

BARRINGTON™

VICTORIAN BRONZE FINISH
CLEAR SEEDY GLASS



1752 VZ
9" DIA., 24¼" H



1754 VZ
9" W, 22½" H



1750 VZ
7½" W, 20¼" H



1751 VZ
9" DIA., 23¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1750 VZ	3-60w Cand.	10½"	10¼"	4½" W, 11½" H Back Plate	
1751 VZ	4-60w Cand.			3" Dia. Post Fitter	
1752 VZ	4-60w Cand.			5¾" Dia. Canopy	6', 5'
1754 VZ	4-60w Cand.	12½"	13¾"	4½" W, 11½" H Back Plate	

For posts and pier mounts, see pages 748-749.

AUGUSTA™

FINISH COPPER BRONZE

GLASS CLEAR BENT, BEVELED AND BOUND PANELS

Augusta's sophisticated beauty showcases its stylish clear bent, beveled and bound glass. Constructed in solid brass with a Copper Bronze finish, this classic traditional design also offers removable scrolls.



2456 CB
16" W, 38¾" H



2452 CB
13" DIA., 27½" H



2454 CB
11" W, 27" H



2443 CB
15¾" DIA., 9" H



2450 CB
9" W, 15½" H



2451 CB
13" DIA., 23¼" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	ADDITIONAL FINISHES
2443 CB	2-60w Med.					MB
2450 CB*	1-60w Med.	8½"	7½"	4½" W, 6½" H Back Plate		
2451 CB	3-40w Cand.			3" Dia. Post Fitter		
2452 CB	3-40w Cand.			5" Dia. Canopy	6', 5'	
2454 CB	3-40w Cand.	10½"	18¼"	4½" W, 15¾" H Back Plate		
2456 CB	4-40w Cand.	14½"	26¼"	5" W, 24" H Back Plate		

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

MONTICELLO™

FINISH COPPER BRONZE

GLASS CLEAR BENT, BEVELED AND BOUND PANELS



Monticello path lights are available in the Hinkley Landscape Lighting Catalog.

Monticello's graceful curves emphasize its clear bent, beveled and bound glass panels. The durable solid brass construction showcases a rich Copper Bronze finish.



2336 CB
16½" W, 26½" H



2332 CB
13" DIA., 20¼" H



2335 CB
13" W, 20½" H



2330 CB
9" W, 15¼" H



2334 CB
11" W, 19¼" H



2331 CB
13" DIA., 21¾" H
(shown as pier mount with 1304 CB)*



2337 CB
16½" DIA., 27" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2330 CB**	1-60w Med.	9¾"	5"	5" W, 7" H Back Plate	
2331 CB	3-40w Cand.			3" Dia. Post Fitter	
2332 CB	3-40w Cand.			5" Dia. Canopy	6', 5'
2334 CB	3-40w Cand.	12½"	6"	4½" W, 9¼" H Back Plate	
2335 CB	3-40w Cand.	13¼"	6¼"	5" W, 9¼" H Back Plate	
2336 CB	4-40w Cand.	15¾"	8"	4½" W, 16" H Back Plate	
2337 CB	4-40w Cand.			3" Dia. Post Fitter	

*Not for use within 4 ft. of ground. **When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

LUCERNE™

FINISH COPPER BRONZE
GLASS CLEAR BENT PANELS

Lucerne's grand silhouette features exquisite decorative cast detailing and solid brass construction in a Copper Bronze finish. Clear bent glass is captured in the fixture's gentle arches.



2315 CB
2315 CB-LED
13¼" W, 30" H





2312 CB
2312 CB-LED
13¼" DIA., 26½" H



2314 CB
2314 CB-LED
10½" W, 24½" H



2310 CB
2310 CB-LED
8½" W, 15" H



2317 CB
2317 CB-LED
10½" DIA., 22¼" H
(shown as
pier mount with
1304 CB)*



2311 CB
2311 CB-LED
13¼" DIA., 26½" H



ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2310 CB	2-40w Cand.	2310 CB-LED	1-10w UNI-60	10½"	3½"	4½" W, 7½" H Back Plate	
2311 CB	4-40w Cand.	2311 CB-LED	1-15w LESM-100			3" Dia. Post Fitter	
2312 CB	4-40w Cand.	2312 CB-LED	1-15w UNI-100			5" Dia. Canopy	6', 5'
2314 CB	3-40w Cand.	2314 CB-LED	1-15w UNI-100	13¾"	11¾"	5" W, 16" H Back Plate	
2315 CB	4-40w Cand.	2315 CB-LED	1-15w UNI-100	17¼"	13½"	5" W, 16½" H Back Plate	
2317 CB	3-40w Cand.	2317 CB-LED	1-15w LESM-100			3" Dia. Post Fitter	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 748-749.

CLIFTON BEACH™

FINISH ANTIQUE COPPER
GLASS CLEAR SEEDY BOUND

Clifton Beach is an aristocratic style that adds a dignified air to a home's façade. The lustrous Antique Copper finish, durable solid brass construction and clear seedy bound glass add to the genteel design.



2268 AP
12½" W, 25½" H



2262 AP
9½" DIA., 19" H



2263 AP
9½" W, 14¾" H



2260 AP
6¾" W, 11" H



2265 AP
9½" W, 17¾" H



2261 AP
12½" DIA., 24" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2260 AP*	1-60w Med.	6½"	4½"	4¾" W, 5½" H Back Plate	
2261 AP	3-40w Cand.			3" Dia. Post Fitter	
2262 AP	3-40w Cand.			5" Dia. Canopy	6', 5'
2263 AP*	1-75w Med.	8¾"	6"	4¾" W, 7" H Back Plate	
2265 AP	2-40w Cand.	9"	11¼"	4¾" W, 12¾" H Back Plate	
2268 AP	3-40w Cand.	11½"	16½"	4¾" W, 18" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

CLIFTON PARK™

FINISH COPPER BRONZE
GLASS CLEAR, BEVELED AND BOUND

Clifton Park has an aristocratic style that adds a dignified air to a home's façade. The sleek Copper Bronze finish, durable solid brass construction and clear beveled and bound glass add to the genteel style.



2429 CB
12½" DIA., 6¾" H



2420 CB
6¾" W, 10¾" H



2428 CB
12½" W, 25½" H



2426 CB
10½" W, 21½" H



2406 CB
17½" W, 36" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE
2406 CB	4-40w Cand.	16"	21¾"	4¾" W, 27¼" H
2420 CB*	1-60w Med.	6½"	4½"	4¾" W, 5½" H
2426 CB	3-40w Cand.	10"	14"	4¾" W, 14¼" H
2428 CB	3-40w Cand.	11½"	15¼"	4¾" W, 18¼" H
2429 CB	2-60w Med.			

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7.



2422 CB
10½" DIA., 19" H



2424 CB
10½" W, 18½" H



2425 CB
9½" W, 17¾" H



2423 CB
9¼" W, 14¾" H



2421 CB
12½" DIA., 23¾" H



2407 CB
17½" DIA., 26½" H

ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
2407 CB	4-40w Cand.			3" Dia. Post Fitter	
2421 CB	3-40w Cand.			3" Dia. Post Fitter	
2422 CB	3-40w Cand.			5" Dia. Canopy	6', 5'
2423 CB*	1-75w Med.	8½"	6¼"	4¾" W, 7" H Back Plate	
2424 CB	3-40w Cand.	10"	7"	4¾" W, 7" H Back Plate	
2425 CB	2-40w Cand.	8½"	11¼"	4¾" W, 12¾" H Back Plate	

*When fitted with DSL-40, this item is Dark Sky compliant, see page 7. For posts and pier mounts, see pages 748-749.

LUNA™ STEP

FINISH BRONZE, LIGHT ALMOND,
MATTE BRONZE, SATIN WHITE, TITANIUM

The Luna step light is the perfect addition to any interior or exterior lighting plan and complements the Hinkley Luna outdoor lantern collection. A contemporary styled radius front die cast faceplate is included. The Luna step light is compatible with any decorator style faceplate and is easily retrofitted to any gang/receptacle location.

THE PERFECT SOLUTION FOR ANY INDOOR OR OUTDOOR 120V OUTLET OR SWITCH LOCATION

- Single or Double Gang Configuration
- Die-Cast Zinc Aluminum Alloy
- 4w Power Consumption
- Dimmable



58506 LA
4½" W, 4½" H



58506 SW
4½" W, 4½" H



DOUBLE GANG CONFIGURATION



58506 TT
4½" W, 4½" H



58506 BZ
4½" W, 4½" H





top view showing profile radius



top view showing profile radius



58504 LA
3" W, 4½" H





58504 SW
3" W, 4½" H









58504 TT
3" W, 4½" H





58504 MZ
3" W, 4½" H







58504 BZ
3" W, 4½" H





SINGLE GANG CONFIGURATION

Compatible with any decorator style faceplate





58508 LA
4½" W, 3" H







58508 SW
4½" W, 3" H





58508 TT
4½" W, 3" H





58508 MZ
4½" W, 3" H





58508 BZ
4½" W, 3" H





side view
showing
profile radius

ITEM	INTEGRATED LED LIGHT SOURCE	EXT.
58504 BZ, LA, MZ, SW, TT	1-4w LS-20	½"
58506 BZ, LA, SW, TT	1-4w LS-20	½"
58508 BZ, LA, MZ, SW, TT	1-4w LS-20	½"



**EMBRACE
ECO-CHIC**

ALL HINKLEY
LANDSCAPE
LIGHTING IS
AVAILABLE
IN LED!

enchanting EXTERIORS

EXPAND YOUR ENVIRONMENT WITH HINKLEY'S
WIDE SELECTION OF **LANDSCAPE LIGHTING**

The purpose of landscape lighting is to unify the relationship between your house and the landscaping that surrounds it. One of the great features of landscape lighting is that it allows you to start slowly and gradually add in more lights as your time, budget or exterior space allows. You may choose to begin with path lights to add safety to your walkways and then slowly fill in various accent lights to emphasize features of your landscaping.

Landscape lighting enhances your outdoor living environment, extends the hours of enjoyment you and your family spend outdoors and provides safety and security. Well-designed landscape lighting will reinforce aesthetic appeal and increasingly add more value to your home.

Residential outdoor lighting is an amenity that requires careful consideration and research. Hinkley offers a variety of tools to help you along the way. Explore our full-line Landscape Lighting catalog, learn from our easy-to-follow educational videos or visit us online at hinkleylandscapelighting.com for detailed guidelines, tips and recommendations. If you decide to enlist the help of an expert, use our convenient showroom locator to find professional lighting consultants in your area.

SATURN 1579 SS, HINKLEY'S LANDSCAPE
LIGHTING CATALOG AND 1901 SS, PAGE 577

WE'VE GOT YOU COVERED:

CHECK OUT HINKLEYLANDSCAPELIGHTING.COM
TO ILLUMINATE YOUR OUTDOOR ENVIRONMENT



PATH



ACCENT



SPOT



DECK & STEP

PATH: ATLANTIS 1518 HE | ACCENT: NEXUS 15450 BZ | SPOT: HARDY ISLAND 1536 MZ | DECK: 1546 BZ

COORDINATE & COMPLEMENT

LOOK FOR THE FOLLOWING COLLECTIONS IN HINKLEY'S
OUTDOOR SECTION THAT OFFER COORDINATING LANDSCAPE
LIGHTING OPTIONS:



ATLANTIS
582-587



SATURN
572-577



SHELTER
604-609



HARBOR
560-565



RALEY
698-701



TRELLIS
684-686

View our complete collection of path lights in the Hinkley Landscape Lighting catalog.



“Planning for the experience of sitting at the dinner table and looking outside across a landscaped lawn—with highlights on trees, paths and patios—ensures that

GOOD DESIGN EXTENDS BEYOND THE INTERIOR ENVIRONMENT.”

HEATHER GARRETT
HEATHER GARRETT INTERIOR DESIGN
DURHAM, NC

PIER MOUNTS



1301 BK



1304 BK



1304 BZ



1304 CB



1304 DZ



1304 HE



1304 KZ



1304 MB



1304 OB



1304 OZ



1304 RB



1304 SN



1305 OB



1307 BG



1307 MN



1307 MO



1307 MR



1307 PZ



1307 RK



1307 VK



1307 VZ



1308 AP



1308 MT

ITEM	FINISH	DIAMETER	BASE HEIGHT	FITTER DIAMETER
1301 BK	Black	3"	¼"	3"
1304 BK*	Black	7"	2"	3"
1304 BZ*	Bronze	7"	2"	3"
1304 CB*	Copper Bronze	7"	2"	3"
1304 DZ*	Aged Zinc	7"	2"	3"
1304 HE*	Hematite	7"	2"	3"
1304 KZ*	Buckeye Bronze	7"	2"	3"
1304 MB*	Museum Black	7"	2"	3"
1304 OB*	Olde Bronze	7"	2"	3"
1304 OZ*	Oil Rubbed Bronze	7"	2"	3"
1304 RB*	Regency Bronze	7"	2"	3"
1304 SN*	Sienna	7"	2"	3"

ITEM	FINISH	DIAMETER	BASE HEIGHT	FITTER DIAMETER
1305 OB	Olde Bronze	7"	2"	3"
1307 BG	Black Granite	7"	2"	3"
1307 MN	Midnight Bronze	7"	2"	3"
1307 MO	Mocha	7"	2"	3"
1307 MR	Museum Bronze	7"	2"	3"
1307 PZ	Pearl Bronze	7"	2"	3"
1307 RK	River Rock	7"	2"	3"
1307 VK	Vintage Black	7"	2"	3"
1307 VZ	Victorian Bronze	7"	2"	3"
1308 AP	Antique Copper	7"	2"	3"
1308 MT	Metro Bronze	7"	2"	3"

Mounting hardware not included. *Concealed fasteners.

POSTS



ITEM	DIAMETER	HEIGHT	FITTER DIAMETER	WALL THICKNESS	CONSTRUCTION	ACCESSORIES INCLUDED/NOTES
6610 BK	3"	10'	3"	.072"	One-Piece Post, Aluminum	Ground Outlet, Photo Cell
6611 BK	3"	10'	3"	.072"	One-Piece Post, Aluminum	Photo Cell
6638 BK	3"	6½'	3"	.080"	Post, Cast Aluminum	Cast Aluminum Base
6660 BK	3"	7'	3"	.050"	One-Piece Post, Aluminum	
6660 BZ	3"	7'	3"	.050"	One-Piece Post, Aluminum	
6660 OI	3"	7'	3"	.050"	One-Piece Post, Aluminum	
6661 BK*	3"	7'	3"	.050"	One-Piece Post with Ladder Rest, Aluminum	
6662 BK	3"	7'	3"	.050"	One-Piece Post, Aluminum	Photo Cell
6663 BK*	3"	7'	3"	.050"	One-Piece Post with Ladder Rest, Aluminum	Photo Cell
6667 BK*	3"	7'	3"	.050"	One-Piece Post with Ladder Rest, Aluminum	Photo Cell and Ground Outlet
6680 BK	7¼"	18¼"	3"		Slip Base, Die Cast Aluminum	2-Piece, Used with Direct Burial Posts
6808 BK	10½"	8'	3"	.125"	Post, Cast Aluminum	Decorative Flange Bolt Cover

*Width including ladder rest is 16".

welcome to
LIGHTING 101

ILLUMINATING INFORMATION

Hinkley is here to be your go-to guide for lighting tips, trends and technical how-tos. Welcome to **LIGHTING 101**: a quick lesson in the basic terms and measurements to assist you in sizing and selecting a home full of fixtures.

LIGHTING MADE SIMPLE

For additional guidance, tips and lighting trends, check out Lighting Made Simple (Hinkley's Guide to Lighting for Real Life). Visit hinkleylighting.com to order a copy! Features include:

7 EASY STEPS TO CHOOSING THE RIGHT LIGHT
 download your coordinating worksheet at hinkleylighting.com

LIGHTING 101 VISUAL DIAGRAM

WORK IT! 7 EASY STEPS TO CHOOSING THE RIGHT LIGHT

For extra help, refer to Lighting 101, Hinkley's go-to guide for selecting and sizing the right lighting. This guide can be found on page 101 in Lighting Made Simple, Hinkley's Guide to Lighting for Real Life.

- 1 select your SPACE**
 FIRST, IDENTIFY THE AREAS YOU WANT TO ENHANCE WITH LIGHTING.
- 2 LIGHTING requirements**
 CHECK IN ON THE REQUIRED LIGHTING FUNCTIONS IN YOUR ROOMS. DIFFERENT ROOMS REQUIRE DIFFERENT LIGHTING.
- 3 MEASURE: the areas to light**
 NEVER MISS TO MEASURE YOUR ROOMS FOR LIGHTING.
- 4 NUMBER of fixtures**
 CHECK YOUR NEEDS FOR HOW MANY FIXTURES YOU WANT TO INSTALL IN EACH ROOM.
- 5 choose a STYLE**
 SELECT DESIGNS THAT WILL STAND OUT IN YOUR SPACE.
- 6 find a FINISH**
 THINK ABOUT HOW THE LIGHTING WILL COMPLEMENT ANY OTHER FINISHES IN YOUR SPACE.
- 7 get creative and HAVE FUN**
 COORDINATE THE STYLE OF THE FIXTURES AND OVER-THE-TOP OF THEM. WILL USE THE RIGHT TOUCH OF FLAIR AND CHARACTER.

HINKLEY
 LIGHTING MADE SIMPLE | HINKLEYLIGHTING.COM



glossary of LIGHTING TERMS

BE IN THE KNOW! **LEARN THE LINGO**

TO HELP YOU SELECT THE PROPER LIGHTING PRODUCT



arm

ACCENT LIGHTING

Lighting that is used to accent or highlight a particular object such as a work of art. To be effective accent lighting should be approximately four or five times the level of ambient light in the room.

ADA (Americans with Disabilities Act)
ADA compliant fixtures do not extend more than 4" from the wall.

AMBIENT LIGHTING

General lighting that usually lights up an entire space.

ARM

A decorative shaped tube or casting that is used to support a socket that usually has socket wires running through it.

BACK PLATE

The part of a fixture that mounts to a wall or vertical surface.

BOBECHE

A disc or decorative plate that sits under the candle sleeve.



bobèche

CANOPY

The decorative plate that attaches to ceiling to cover the junction box.



canopy

COMBINATION MOUNT

Refers to the ability of a fixture to either be hung by chain or mounted directly to the ceiling.



combination mount

CFL (Compact Fluorescent)

An energy efficient fluorescent bulb with a lifespan that is ten times longer and 3 to 4 times more efficient than an incandescent bulb.

DIFFUSER

A shield or shade that softens light intensity and/or prevents the light bulbs from being directly exposed.

DIMMER

A device used for varying the brightness of lamps in a lighting installation. Dimming controls are ideal for almost any type of room because they can change the amount of lighting to suit each mood or activity.

EXTENSION

Refers to the depth of a wall mounted fixture or the measurement from the wall to the farthest point on the fixture away from the wall.



finial

FINIAL

A small finishing ornament at the crown or bottom of a fixture.

FLUSH OR SEMI-FLUSH MOUNT

Sometimes referred to as ceiling mounted fixtures, these fixtures mount directly to the ceiling with a "pan" or canopy.

GLASS OR SHADE

A decorative opaque or translucent covering on light fixtures designed to shield the light source or redirect the light.

LAMPS

Another term for bulbs, also referred to as lamping.

LED (Light Emitting Diode)

Extremely efficient and long lasting solid state lighting. Estimated LED chip life= 40,000 hrs.

PENDANT

These fixtures can be used to provide both task and general lighting. Equipped with shades or globes to avoid glare, they are suspended from the ceiling over tables, kitchen counters or other work areas.

SCONCE

An ornamental light fixture attached to a wall to provide additional layers of light in a room.

TASK LIGHTING

Lighting that is specifically installed to light an area where a task is performed.

TOP TO OUTLET (TTO)

The measurement from the top of the fixture to the center of the outlet box when installed.

TRANSFORMER

An electrical device that transforms the line voltage (usually 120 volts for residential settings or 277 volts for commercial settings) into the voltage that a low voltage lighting system requires (12, 15 or 24 volts).

WATTAGE

The amount of energy consumed by a light bulb.

CHANDELIERS

THE PERFECT CHANDELIER IS THE STANDOUT SHOWPIECE OF A HOME. OUR SIZING TIPS AND SUGGESTIONS WILL HELP YOU FIND THE RIGHT FIT TO MAKE YOUR SPACE SHINE.

FOYER LIGHTING

High and spacious ceilings lend well to the use of one large or multiple chandeliers to create a grand entrance. If your foyer has a second story window, center your chandelier so it is easily seen from outside the home.



PLYMOUTH 4254OB, PAGE 135



THE BOTTOM OF DINING ROOM FIXTURES SHOULD SIT APPROXIMATELY
32"-34"
 FROM THE TABLE TOP

CLANCY 3034KZ, PAGE 180

DON'T FORGET TO DIM!

Ensuring your dining room lighting is on a dimmer is a must for added flexibility in creating the appropriate environment. The atmosphere of Sunday brunch differs from that of a dinner party, and lighting is a crucial element in setting the right mood.

Chandeliers make a statement in all areas of your home: kitchens, dining rooms, foyers, living rooms, and even in smaller spaces such as a reading nook. For more ideas and unexpected applications, visit the Chandelier Idea Center on pages 47-52.



MIME FR4560BNI, PAGE 341

SCONCES ARE
RECOMMENDED TO
BE SPACED
6'-8'
APART, WITH THE CENTER
OF THE LIGHT SOURCE
66"
FROM THE FLOOR



SCONCES

Versatile and available in an extremely wide variety of styles and finishes, sconces add a key visual interest to your walls. In larger areas such as foyers or spacious dining rooms, sconces are a stylish solution to supplement chandeliers.

PENDANTS

Whether your space allows for a single pendant as a solo style statement or a grouping for a sizable impact, pendants are a great go-to for decorative task lighting. Keep in mind that when placed in an area where people tend to gather, such as a kitchen island, that pendants should be installed high enough that people can see one another, but not so high that they are blinded by the glare of the bulbs.

A RECOMMENDED RANGE TO HANG
PENDANTS IS WITH THE BOTTOM OF THE FIXTURE
28"-34"
FROM THE COUNTERTOP



FLUSH & SEMI-FLUSH MOUNTS

A staple in lighting design, flush and semi-flush mounts add a decorative flair to any space and are an easy way to add overhead ambient lighting. The bottom of a fixture should be no lower than 7' from the floor, making a flush mount the best option for rooms with lower ceilings, and a semi-flush when ceiling height allows.

To determine size, add the length and width of a room in feet and that number, in inches, is the guideline for the fixture's diameter.

10' X 10' ROOM: 20' (20" DIAMETER FIXTURE)



bath & VANITY



INSTALL SCONCES
36"-40"
 APART, WITH THE CENTER
 OF THE LIGHT SOURCE
 APPROXIMATELY
66"
 FROM THE FLOOR

A MINIMUM OF
150 WATTS
 OF INCANDESCENT
 EQUIVALENT LIGHT
 SHOULD BE USED
 TO LIGHT A VANITY

MIRA FIZZ FR55453PCM, PAGE 428 | CIRRUS 3802BN, PAGE 213

SCONCES

Properly installed task lighting in the bathroom is a must for grooming, such as applying makeup or shaving. The ideal application is to have fixtures mounted on either side of a mirror to eliminate unnecessary shadows.

Sconces should generally be installed 36"-40" apart from one another, with the center of the light source at eye level, approximately 66" from the floor.

A bare minimum of light output equivalent to 150 watts of incandescent light should be used in lighting the vanity, and it is always safer to initially err on the side of too much wattage. In cases where you find there is too much light, either use lower wattage bulbs or install a dimmer.

BATH BARS

If sconces are not an option for your bathroom because of space or design constraints, a bath bar above a vanity is an ideal selection for adding style and substance to your space.

A BATH BAR OVER A VANITY
 SHOULD BE AT LEAST
24"
 WIDE AND MOUNTED
75"-80"
 FROM THE FLOOR

Consider layering light in your bathroom for the perfect mix of task and ambient illumination. A flush or semi-flush mount is a functional and decorative complement to vanity lighting.



BROOKE 53003AN, PAGE 502

Outdoor LIGHTING

ILLUMINATING THE EXTERIOR OF YOUR HOME EXPANDS YOUR LIVING ENVIRONMENT, HEIGHTENS CURB APPEAL AND ADDS SAFETY TO ANY OUTDOOR SPACE.

OUTDOOR LANTERNS

Entryway lighting is the optimal accessory to the facade of your home, serving as a welcoming feature for your family and guests. Keep in mind that when selecting decorative outdoor lighting, it is best to stay true to the period and architectural style of your home's exterior.

TWO OUTDOOR LANTERNS ON EITHER SIDE OF AN ENTRYWAY SHOULD APPEAR TO BE

$\frac{1}{4}$

THE SIZE OF THE DOOR FROM A DISTANCE ($\frac{1}{8}$ FOR A SINGLE LANTERN)



SHELTER 1325BK, PAGE 606



SATURN 1901SS, PAGE 579
SATURN 1579SS

HELPFUL TIP

TAKE CARE TO INSTALL FIXTURES OUT OF THE GRASS OR IN AREAS THAT WILL NOT INTERFERE WITH MOWING OR OTHER LANDSCAPING TASKS.

PATH LIGHTS

Landscape lighting plays an integral part in highlighting the natural environment surrounding your home. By installing path lights, shrubs and flower beds will shine bright even at night, and walkways remain visible for after hours use.

View the full line Hinkley Landscape Lighting catalog for all path light options.

INSTALLING PATH LIGHTS APPROXIMATELY

6'


APART WILL ENSURE ADEQUATE BEAM SPREAD AND A SAFELY LIT WALKWAY



EXPLORE HINKLEY'S ENERGY EFFICIENT OPTIONS IN LED, GU24 AND DARK SKY TO ADD AN ECO-CHIC ELEMENT TO YOUR HOME.

STAY *CONNECTED*

DISCOVER **HINKLEYLIGHTING.COM**



STAY IN TOUCH WITH HINKLEY LIGHTING AND BE INSPIRED BY UP-TO-THE-MINUTE PRODUCTS, TRENDS AND HAPPENINGS. BE SURE TO CHECK OUT OUR OTHER SITES AT **FREDRICKRAMOND.COM** AND **HINKLEYLANDSCAPELIGHTING.COM** FOR A FULL SPECTRUM OF LIGHTING.

FIND
LIGHTING *love*
YOU WILL

Explore the digital version of our catalogs and be inspired by the home décor tips, style guides and product videos in our online Idea Center. Enjoy shopping by style, application and finish to find lighting you will love.

TALK IS **CHIC** LET'S BE **SOCIAL** #hinkleylighting #lifeaglow



YOUTUBE

[YOUTUBE.COM/HINKLEYLIGHTINGINC](https://www.youtube.com/hinkleylightinginc)
Watch our informative product and engaging brand videos.



HOZZ

[HOZZ.COM/HINKLEYLIGHTING](https://www.houzz.com/hinkleylighting)
Discover our products in all types of places and spaces.



TWITTER

[TWITTER.COM/HINKLEYLIGHTING](https://twitter.com/hinkleylighting)
Join the conversation and hear what Hinkley has to say.



FACEBOOK

[FACEBOOK.COM/HINKLEYLIGHTING](https://www.facebook.com/hinkleylighting)
Keep up with current Hinkley activity.



PINTEREST

[PINTEREST.COM/HINKLEYLIGHTING](https://www.pinterest.com/hinkleylighting)
Find out what inspires us.



INSTAGRAM

[INSTAGRAM.COM/HINKLEYLIGHTING](https://www.instagram.com/hinkleylighting)
See what's happening around Hinkley.

CATALOG INDEX

1100		1280VZ	655	1325HE	606	1430RB	686	1645TT	583	1704BK	719
1120MR	625	1281VZ	655	1325KZ	608	1431RB	685	1646BZ	585	1705BK	718
1120VK	623	1282VZ	655	1326BK	605	1432RB	686	1646SK	587	1707BK	719
1121MR	625	1284VZ	655	1326HE	607	1433RB	685	1646TT	583	1713BG	711
1121VK	623	1285VZ	654	1326KZ	609	1433RB-SCR	685	1647BZ	580	1720BG	711
1122MR	625	1286VZ	655	1328BK	605	1434RB	686	1647SK	580	1721BG	711
1122VK	623			1331MB	715	1435RB	684	1647SW	580	1722BG	711
1124MR	625	1300		1331MO	714	1436RB	686	1647TT	580	1725BG	711
1124VK	623	1301BK	748	1332MB	715	1437RB	685	1648BZ	585	1726BG	710
1125MR	625	1304BK	748	1332MO	714	1438RB	685	1648SK	587	1741BK	631
1125VK	623	1304BZ	748	1334MB	715	1439RB	686	1648TT	583	1741OZ	630
1126MR	625	1304CB	748	1334MO	714	1440BK	721	1649BZ	585	1742BK	631
1126VK	623	1304DZ	748	1335MB	715	1441BK	720	1649SK	587	1742OZ	630
1129MR	624	1304HE	748	1335MO	714	1445BK	720	1649TT	583	1744BK	631
1129VK	622	1304KZ	748	1336MB	715	1449BK	721	1650BZ	585	1744OZ	630
1140OL	691	1304MB	748	1336MO	714	1470BK	721	1650TT	583	1745BK	631
1141OL	691	1304OB	748	1350MB	657	1471BK	720	1655BZ	585	1745OZ	630
1142OL	691	1304OZ	748	1350OZ	656	1490AM	675	1655TT	583	1750VZ	733
1144OL	691	1304RB	748	1351MB	657	1490BK	677	1660BZ	579	1751VZ	733
1145OL	690	1304SN	748	1351OZ	656	1491AM	675	1660SK	579	1752VZ	733
1150RB	621	1305OB	748	1352MB	657	1491BK	677	1660TT	579	1754VZ	733
1151RB	621	1307BG	748	1352OZ	656	1492AM	675	1663BZ	580	1760BZ	594
1152RB	621	1307MN	748	1354MB	657	1492BK	677	1663SK	580	1760SK	594
1154RB	621	1307MO	748	1354OZ	656	1494AM	675	1663TT	580	1760TT	594
1155RB	621	1307MR	748	1356MB	657	1494BK	677	1664BZ	579	1761BZ	595
1180SN	537	1307PZ	748	1356OZ	656	1495AM	674	1664SK	578	1761SK	595
1181SN	537	1307RK	748	1380BK	722	1495BK	676	1664TT	579	1761TT	595
1182SN	537	1307VK	748	1381BK	722	1499AM	675	1666BZ	581	1763BZ	595
1184SN	537	1307VZ	748	1382BK	722	1499BK	677	1666SK	581	1763SK	595
1185SN	536	1308AP	748	1384BK	722			1666TT	581	1763TT	595
1187SN	537	1308MT	748	1385BK	722	1600		1667BZ	581	1764BZ	594
		1311MB	713	1390BK	617	1600MB	701	1667SK	581	1764SK	594
		1311MO	712	1390BZ	619	1600OZ	699	1667TT	581	1764TT	594
1200		1312MB	713	1391BK	617	1601MB	701	1670BK	727	1766BZ	596
1200SN	531	1312MO	712	1391BZ	619	1601OZ	699	1670OZ	725	1766SK	596
1201SN	531	1314MB	713	1392BK	617	1602MB	701	1671BK	727	1766TT	596
1202SN	531	1314MO	712	1392BZ	619	1602OZ	699	1671OZ	725	1767BZ	596
1204SN	531	1315MB	713	1394BK	617	1604MB	701	1672BK	727	1767SK	596
1205SN	530	1315MO	712	1394BZ	619	1604OZ	699	1672OZ	725	1767TT	596
1240MN	717	1316MB	713	1395BK	616	1605MB	701	1674BK	727	1770SN	533
1241MN	717	1316MO	712	1395BZ	618	1605OZ	699	1674OZ	725	1771SN	533
1242MN	717	1319MB	713	1396BK	617	1609MB	700	1675BK	726	1772SN	533
1243MN	717	1319MO	712	1396BZ	619	1609OZ	698	1675OZ	724	1774SN	533
1244MN	717	1320BK	605	1397BK	617	1639BZ	584	1676BK	727	1775SN	532
1245MN	716	1320HE	607	1397BZ	619	1639SK	586	1676OZ	725	1790BK	669
1270OZ	659	1320KZ	609			1639TT	582	1677BK	727	1791BK	669
1270VK	661	1321BK	605	1400		1640BZ	585	1677OZ	725	1792BK	669
1271OZ	659	1321HE	607	1410BK	721	1640SK	587	1683BK	727	1794BK	668
1271VK	661	1321KZ	609	1412BK	720	1640TT	583	1683OZ	725	1797BK	669
1272OZ	659	1322BK	605	1419BK	721	1641BZ	585	1696KZ	620		
1272VK	661	1322HE	607	1420AI	689	1641SK	587	1697KZ	620	1800	
1273OZ	659	1322KZ	609	1421AI	689	1641TT	583	1698KZ	620	1800BK	645
1273VK	661	1324BK	605	1422AI	689	1644BZ	585	1699KZ	620	1800OP	646
1274OZ	659	1324HE	607	1424AI	689	1644SK	587			1800OZ	644
1274VK	661	1324KZ	609	1425AI	688	1644TT	583	1700			
1275OZ	658	1325BK	604	1429RB	685	1645BZ	585	1700BK	719		
1275VK	660					1645SK	587	1702BK	719		

1801BK	645	1908SS	577	2014OZ	634	2184BZ	598	2261AP	741	2428CB	742
1801OP	646	1909MT	574	2015OZ	634	2184SK	599	2262AP	741	2429CB	742
1801OZ	644	1909SK	572	2020BZ	612	2185BZ	598	2263AP	741	2430GS	672
1802BK	645	1909SS	576	2020TT	613	2185SK	599	2265AP	741	2430OZ	673
1802OP	646	1910OZ	557	2021BZ	612	2190BZ	615	2268AP	740	2434GS	672
1802OZ	644	1911OZ	557	2021TT	613	2190TT	614	2271AM	679	2434OZ	673
1804BK	645	1912OZ	557	2024BZ	612	2191BZ	615	2272AM	679	2435GS	672
1804OP	646	1914OZ	557	2024TT	613	2191TT	614	2274AM	679	2435OZ	673
1804OZ	644	1915OZ	556	2025BZ	612	2192BZ	615	2275AM	678	2440CB	729
1805BK	645	1921BK	705	2025TT	613	2192TT	614	2278AM	679	2440MB	731
1805OP	646	1921RK	703	2026BZ	612	2194BZ	615	2290SN	539	2441CB	729
1805OZ	644	1929BK	704	2026TT	613	2194TT	614	2291SN	539	2441MB	731
1819BK	720	1929RK	702	2040GS	545	2195BZ	615	2292SN	539	2442CB	729
1830BZ	592	1930RB	693	2040SN	543	2195TT	614	2294SN	539	2442MB	731
1830SK	592	1931RB	693	2041GS	545			2295SN	539	2443CB	729
1830TT	592	1932RB	693	2041SN	543			2297SN	539	2443MB	731
1831BZ	593	1934RB	693	2042GS	545	2200		2298SN	538	2444CB	729
1831SK	593	1935RB	692	2042SN	543	2200DZ	643			2444MB	731
1831TT	593	1936RB	693	2044GS	545	2200SZ	641	2300		2445CB	729
1834BZ	592	1940FZ	707	2044SN	543	2201DZ	643	2300KZ	603	2446CB	728
1834SK	592	1940MB	706	2045GS	544	2201SZ	641	2302KZ	603	2446MB	730
1834TT	592	1941FZ	707	2045SN	542	2202DZ	643	2304KZ	603	2447CB	729
1840BK	547	1941MB	706	2045GS	542	2202SZ	641	2305KZ	602	2447MB	731
1841BK	547	1942FZ	707	2047GS	545	2203DZ	643	2306KZ	603	2450CB	735
1842BK	547	1942MB	706	2047SN	543	2203SZ	641	2310CB	739	2451CB	735
1844BK	547	1944FZ	707	2050HE	589	2204DZ	643	2311CB	739	2452CB	735
1845BK	546	1944MB	706	2050KZ	589	2204SZ	641	2312CB	739	2454CB	735
1851DZ	535	1946FZ	707	2050TT	589	2205DZ	642	2314CB	739	2456CB	734
1852DZ	535	1946MB	706	2054HE	588	2205SZ	640	2315CB	738	2460OZ	525
1854DZ	535	1950HE	648	2054KZ	589	2206DZ	643	2317CB	739	2461OZ	525
1855DZ	535	1950VZ	649	2054TT	589	2206SZ	641	2320OZ	567	2462OZ	525
1858DZ	534	1951HE	648	2060BZ	610	2207DZ	643	2321OZ	567	2464OZ	525
1890BK	705	1951HE	648	2060SK	611	2207SZ	641	2322OZ	567	2465OZ	524
1890RK	703	1951VZ	649	2064BZ	610	2210GS	628	2324OZ	567	2468OZ	525
1891BK	705	1952HE	648	2064SK	611	2210OZ	627	2325OZ	566	2470OZ	629
1891RK	703	1952VZ	649	2065BZ	610	2214GS	628	2327OZ	567	2471OZ	629
1892BK	705	1954HE	648	2065SK	611	2214OZ	627	2330CB	737	2472OZ	629
1892RK	703	1954VZ	649	2080SB	647	2220CB	697	2331CB	737	2474OZ	629
1894BK	705	1956HE	648	2081SB	647	2221CB	697	2332CB	737	2475OZ	629
1894RK	703	1956VZ	649	2082SB	647	2222BB	147	2334CB	737		
1895BK	705	1960OZ	663	2084SB	647	2222CB	697	2335CB	737	2500	
1895RK	703	1961OZ	663	2090SB	635	2222PL	141	2336CB	736	2500BK	723
1898BK	705	1962OZ	663	2091SB	635	2222PZ	144	2337CB	737	2501BK	723
1898RK	703	1964OZ	663	2092SB	635	2224CB	697	2350BZ	601	2502BK	723
1899BK	705	1965OZ	662	2094SB	635	2225CB	696	2350SS	601	2504BK	723
1899RK	703	1970BK	555	2095SB	635	2226CB	697	2354BZ	601	2505BK	723
		1972BK	555			2227CB	697	2354SS	601	2570AR	563
		1974BK	554	2100		2227CB	697	2355BZ	600	2570SK	565
1900		1980BK	665	2110BZ	591	2230OZ	569	2355SS	600	2570TT	561
1900MT	575	1980OZ	664	2110TT	591	2231OZ	569	2370AS	541	2571AR	563
1900SK	573	1981BK	665	2114BZ	591	2232OZ	569	2371AS	541	2571SK	565
1900SS	577	1981OZ	664	2114TT	591	2234OZ	569	2372AS	541	2571TT	561
1901MT	575	1982BK	665	2115BZ	590	2235OZ	568	2374AS	540	2572AR	563
1901SK	573	1982OZ	664	2115TT	590	2240RB	681	2376AS	541	2572SK	565
1901SS	577	1984BK	665	2120PZ	695	2241RB	681			2572TT	561
1902MT	575	1984OZ	664	2121PZ	695	2242RB	681	2400		2573AR	563
1902SK	573	1990OZ	667	2122PZ	695	2243RB	681	2406CB	742	2573SK	565
1902SS	577	1991OZ	667	2123PZ	695	2244RB	680	2407CB	743	2573TT	561
1904MT	575	1992OZ	667	2124PZ	694	2246RB	681	2420CB	742	2574AR	563
1904SK	573	1994OZ	667	2126PZ	695	2250BK	637	2421CB	743	2574SK	565
1904SS	577	1995OZ	666	2128PZ	695	2251BK	637	2422CB	743	2574TT	561
1905MT	575			2150KZ	670	2252BK	637	2423CB	743	2575AR	563
1905SK	573	2000		2154KZ	670	2254BK	637	2424CB	743	2575SK	565
1905SS	577	2010OZ	634	2155KZ	670	2255BK	637	2425CB	743	2575TT	561
1908MT	575	2011OZ	634	2180BZ	598	2258BK	636	2426CB	742	2576AR	563
1908SK	573	2012OZ	634	2180SK	599	2260AP	741				

2576SK	565	2902RB	709	3042CM	265	3127CM	277	3150OZ	266	3209BR	210
2576TT	561	2903RB	709	3042OZ	265	3127KZ	277	3151AN	267	3209KZ	202
2579AR	562	2904RB	709	3043AN	265	3127PL	277	3151CM	267	3210AN	206
2579SK	564	2905RB	708	3043CM	265	3128AN	272	3151OZ	267	3210BR	210
2579TT	560	2910OZ	553	3043OZ	265	3128CM	272	3161OZ	219	3210KZ	202
		2911OZ	553	3044AN	264	3128OZ	272	3162OZ	219	3211AN	205
2600		2914OZ	553	3044CM	264	3129AN	272	3163OZ	218	3211BR	209
2611OZ	633	2915OZ	552	3044OZ	264	3129CM	272	3164OZ	219	3211KZ	201
2612OZ	633	2920BZ	570	3045AN	265	3129OZ	272	3170AN	268	3212AN	207
2614OZ	633	2920PS	571	3045CM	265	3130AN	273	3170CM	268	3212BR	211
2615OZ	632	2922BZ	570	3045OZ	265	3130CM	273	3170OZ	268	3212KZ	203
2618OZ	633	2922PS	571	3046AN	264	3130OZ	273	3171AN	268	3214AN	206
2620DZ	551	2924BZ	570	3046CM	264	3131AN	273	3171CM	268	3214BR	210
2624DZ	551	2924PS	571	3046OZ	264	3131CM	273	3171OZ	268	3214KZ	202
2625DZ	550	2925BZ	570	3047AN	264	3131OZ	273	3172AN	268	3217AN	207
2630OB	653	2925PS	571	3047CM	264	3133AN	273	3172CM	268	3217BR	211
2631OB	653	2989SN	683	3047OZ	264	3133CM	273	3172OZ	268	3217KZ	203
2632OB	653	2990SN	683	3048AN	263	3133OZ	273	3173AN	268	3220AN	287
2633OB	653	2991SN	683	3048CM	263	3134AN	273	3173CM	268	3220OB	286
2634OB	653	2992SN	683	3048OZ	263	3134CM	273	3173OZ	268	3220OB-WH	285
2635OB	653	2995SN	683	3054AN	274	3134OZ	273	3174AN	268	3221AN	287
2636OB	653	2996SN	682	3054GS	274	3135AN	273	3174CM	268	3221OB	286
2639OB	652			3054HB	274	3135CM	273	3174OZ	268	3221OB-WH	285
2640OB	651	3000		3054RB	274	3135OZ	273	3175AN	268	3222AN	287
2641OB	651	3000OZ	187	3082GF	153	3136AN	272	3175CM	268	3222OB	286
2642OB	651	3000PL	185	3084GF	153	3136CM	272	3175OZ	268	3222OB-WH	285
2643OB	651	3001OZ	187	3085GF	153	3136OZ	272	3176AN	268	3223AN	287
2644OB	651	3001PL	185	3086GF	153	3137AN	272	3176CM	268	3223OB	286
2645OB	651	3002OZ	187	3088GF	152	3137CM	272	3176OZ	268	3223OB-WH	285
2646OB	651	3002PL	185			3137OZ	272	3177AN	268	3224AN	287
2649OB	650	3003OZ	187	3100		3138AN	271	3177CM	268	3224OB	286
2650BK	529	3003PL	185	3110AN	271	3138CM	271	3177OZ	268	3224OB-WH	284
2651BK	529	3004OZ	186	3110CM	271	3138OZ	271	3178AN	269	3225AN	287
2652BK	529	3004PL	184	3110OZ	271	3139AN	272	3178CM	269	3225OB	286
2654BK	529	3005OZ	187	3111AN	271	3139CM	272	3178OZ	269	3225OB-WH	285
2655BK	528	3005PL	185	3111CM	271	3139OZ	272			3226AN	287
		3006OZ	187	3111OZ	271	3140AN	267	3200		3226OB	286
2700		3006PL	185	3112AN	271	3140CM	267	3200AN	205	3226OB-WH	285
2700AR	559	3008OZ	186	3112CM	271	3140OZ	267	3200BR	209	3254BN	275
2700BK	558	3008PL	184	3112OZ	271	3141AN	266	3200KZ	201	3254CM	275
2701AR	559	3009OZ	186	3113AN	269	3141CM	266	3201AN	205	3254OZ	275
2701BK	558	3009PL	184	3113CM	269	3141OZ	266	3201BR	209	3257BN	275
2704AR	559	3013BN	181	3113OZ	269	3143AN	266	3201KZ	201	3257CM	275
2704BK	558	3014BN	181	3114AN	270	3143CM	266	3202AN	206	3257OZ	275
2705AR	559	3015BN	181	3114CM	270	3143OZ	266	3202BR	210	3274BZ	221
2705BK	558	3017BN	181	3114OZ	270	3144AN	267	3202KZ	202	3275BZ	221
2714BZ	597	3031BN	180	3115AN	270	3144CM	267	3203AN	205	3277BZ	221
2714SS	597	3031DZ	180	3115CM	270	3144OZ	267	3203BR	209	3281SL	215
2715BZ	597	3031KZ	180	3115OZ	270	3145AN	266	3203KZ	201	3282SL	215
2715SS	597	3031PN	180	3116AN	270	3145CM	266	3204AN	205	3284SL	215
2780OZ	527	3033BN	179	3116CM	270	3145OZ	266	3204BR	209	3285SL	215
2781OZ	527	3033DZ	179	3116OZ	270	3146AN	266	3204KZ	201	3286SL	215
2782OZ	527	3033KZ	179	3118AN	269	3146CM	266	3205AN	207	3287SL	214
2784OZ	526	3033PN	179	3118CM	269	3146OZ	266	3205BR	211	3291VZ	195
		3034BN	178	3118OZ	269	3147AN	267	3205KZ	203	3292VZ	195
2800		3034DZ	178	3119AN	269	3147CM	267	3206AN	204	3293VZ	195
2860OZ	639	3034KZ	178	3119CM	269	3147OZ	267	3206BR	208	3294VZ	195
2861OZ	639	3034PN	178	3119OZ	269	3148AN	270	3206KZ	200		
2862OZ	639	3040AN	265	3124CM	277	3148CM	270	3207AN	206	3300	
2864OZ	639	3040CM	265	3124KZ	277	3148OZ	270	3207BR	210	3300AN	292
2865OZ	638	3040OZ	265	3124PL	277	3149AN	267	3207KZ	202	3300BR	292
		3041AN	264	3126DZ	276	3149CM	267	3208AN	207	3300CM	292
		3041CM	264	3126KZ	276	3149OZ	267	3208BR	211	3300OZ	292
2900		3041OZ	264	3126PL	276	3150AN	266	3208KZ	203	3301AN	292
2900RB	709	3042AN	265	3126PN	276	3150CM	266	3209AN	206	3301BR	292
2901RB	709										

3301CM	292	3473OB	171	3616PW	160	3805BN	213	4094RI	101	4245OB	133
3301OZ	292	3473PN	175	3620AN	155	3806BN	212	4095RI	101	4245PL	137
3302AN	291	3473PW	173	3620BR	157	3831OB	283	4097RI	101	4246OB	133
3302BR	291	3474HR	177	3622AN	155	3831PL	283	4099RI	100	4246PL	137
3302CM	291	3474OB	171	3622BR	157	3834OB	283			4247OB	134
3302OZ	291	3474PN	175	3623AN	155	3834PL	283	4100		4247PL	138
3304AN	291	3474PW	173	3623BR	157	3851BN	295	4102BB	147	4248OB	133
3304BR	291	3478HR	177	3625AN	155	3851CM	295		515	4248PL	137
3304CM	291	3478OB	171	3625BR	157	3851OZ	295	4102CB	697	4249OB	132
3304OZ	291	3478PN	175	3626AN	155	3852BN	295	4102PL	141	4249PL	136
3305AN	290	3478PW	173	3626BR	157	3852CM	295		514	4254OB	135
3305BR	290	3479HR	176	3628AN	154	3852OZ	295	4102PZ	144	4254PL	139
3305CM	290	3479OB	170	3628BR	156	3870BN	234	4103BB	147	4258OB	135
3305OZ	290	3479PN	174	3629AN	155	3871BN	234	4103PL	141	4258PL	139
3313SB	193	3479PW	172	3629BR	157		475	4103PZ	144	4259OB	135
3314SB	193	3494AN	278	3634OZ	220	3871CM	474	4140BB	146	4259PL	139
3321BN	297	3494HB	278	3636OZ	220	3872BN	234	4140PZ	143		
3321CM	297	3494OZ	278	3636SH	220	3873BN	233	4151OB	099	4300	
3321OZ	297	3497AN	278	3641BN	296	3874BN	234	4161OB	099	4300OL	105
3330BZ	250	3497HB	278	3641CM	296	3875BN	233	4162OB	099	4304OL	105
3332BZ	250	3497OZ	278	3641OZ	296	3876BN	233	4166OB	099	4308OL	104
3334BZ	249			3650HB	239	3877BN	234	4167OB	099	4309OL	102
3335BZ	250	3500		3653HB	239	3878BN	232	4168OB	098	4311OL	105
3336BZ	249	3502OL	104	3654HB	239	3882BN	183	4170VZ	096	4313OL	105
3337BZ	249	3503OL	103	3655HB	238	3885BN	183	4171VZ	096	4314OL	105
3338BZ	248	3504OL	104	3684BN	279	3886BN	182		655	4330CM	071
3341BN	289	3506OL	104	3684BR	279			4173VZ	095	4335CM	071
3341CM	289	3508OL	103	3684CM	279	3900		4174VZ	095	4336CM	071
3342BN	289	3521AN	281	3684OZ	279	3902AN	294	4176VZ	095	4338CM	070
3342CM	289	3521BC	280	3687BN	279	3902CM	294	4177VZ	095	4360KZ	255
3344BN	288	3521CM	282	3687BR	279	3902KZ	294	4178VZ	095	4363KZ	255
3344CM	288	3523AN	281	3687CM	279	3903AN	294	4179VZ	094	4364KZ	254
3380HB	261	3523BC	280	3687OZ	279	3903CM	294	4180BN	065	4367KZ	255
3381HB	261	3523CM	282			3903KZ	294	4186BN	065		
3382HB	261	3524AN	281	3700		3942DZ	253	4188BN	064	4400	
3384HB	261	3524BC	280	3712FB	169	3942KZ	253	4190BN	077	4400GR	151
3385HB	260	3524CM	282	3713FB	169	3944DZ	252	4190TB	079	4401OW	151
		3580PN	223	3714FB	169	3944KZ	252	4193BN	077	4403GR	151
3400		3580VS	225	3716FB	169	3946DZ	253	4193TB	079	4404GR	151
3413BZ	194	3582PN	223	3734AN	192	3946KZ	253	4194BN	077	4405GR	151
3414BZ	194	3582VS	225	3734OZ	192	3951BN	191	4194TB	079	4406GR	151
3440PN	236	3585PN	223	3736AN	192	3953BN	191	4195BN	077	4408GR	150
3441PN	237	3585VS	225	3736OZ	192	3955BN	190	4195TB	079	4410BB	162
3442PN	237	3586PN	223	3752CM	073	3957BN	191	4198BN	076	4410OB	165
3443PN	237	3586VS	225	3756CM	073			4198TB	078	4410PW	159
3444PN	237	3587PN	223	3758CM	072	4000				4412BB	162
3445PN	236	3587VS	225	3782AN	293	4010OL	105	4200		4412OB	165
3446PN	236	3588PN	222	3782HB	293		509	4200HB	061	4412PW	159
3447PN	236	3588VS	224	3782OZ	293	4013OL	103	4200PN	063	4415BB	162
3448PN	235			3783AN	293	4015OL	103	4200SH	061	4415OB	166
3449PN	237	3600		3783HB	293	4016OL	104	4205HB	061	4415PW	160
3460SB	241	3610BB	162	3783OZ	293	4017OL	105	4205PN	063	4416BB	162
3463SB	241	3610OB	166	3793BN	197	4018OL	103	4206HB	060	4416OB	165
3466SB	241	3610PW	160	3793KZ	199	4019OL	103	4206PN	062	4416PW	159
3468SB	241	3612BB	163	3794BN	197	4020AN	075	4240OB	134	4417BB	162
3469SB	240	3612OB	166	3794KZ	199	4021AN	075	4240PL	138	4417OB	165
3470HR	177	3612PW	160	3796BN	196	4023AN	075	4241OB	134	4417PW	159
3470OB	171	3613BB	163	3796KZ	198	4024AN	075	4241PL	138	4419BB	161
3470PN	175	3613OB	166	3797BN	197	4025AN	075		506	4419OB	164
3470PW	173	3613PW	160	3797KZ	199	4027AN	075	4242OB	134	4419PW	158
3472HR	177	3614BB	163			4028AN	074	4242PL	138	4421OW	162
3472OB	171	3614OB	166	3800		4033RB	251	4243OB	133	4430KZ	089
3472PN	175	3614PW	160	3800BN	213	4034RB	251	4243PL	137	4431KZ	089
3472PW	173	3616BB	163	3802BN	213	4037RB	251	4244OB	134	4433KZ	089
3473HR	177	3616OB	166	3804BN	213	4090RI	101	4244PL	138	4434KZ	089

4436KZ	089	4633TB	085	4664OB	115	4795BN	124	4956HB	055	50031OZ	485
4437KZ	089	4636BN	081	4664OB-OPAL	111	4795EZ	127	4956LZ	057	50032AN	485
4438KZ	089	4636OZ	083	4665BN	119	4796BN	123	4956PL	059	50032CM	485
4439KZ	088	4636TB	085	4665OB	115	4796EZ	126	4958HB	055	50032OZ	485
4470TB	087	4637BN	081	4665OB-CL	107	4797BN	124	4958LZ	057	50033AN	485
4473TB	087	4637OZ	083	4665OB-OPAL	111	4797EZ	127	4958PL	059	50033CM	485
4474TB	087	4637TB	085	4666BN	118	4798BN	123	4959HB	054	50033OZ	485
4475TB	087	4638BN	081	4666OB	114	4798EZ	126	4959LZ	056	50034AN	485
4478TB	086	4638OZ	083	4666OB-OPAL	110	4799BN	122	4959PL	058	50034CM	485
		4638TB	085	4667BN	117	4799EZ	125	4960OB	129	50034OZ	485
		4639BN	080	4667OB	113			4962OB	129	50035AN	485
4500		4639OZ	082	4667OB-OPAL	109	4800		4964OB	129	50035CM	485
4505VZ	096	4639TB	084	4669BN	119	4850BC	229	4965OB	129	50035OZ	485
4508VZ	096	4640BB	163	4669OB	115	4850BN	227	4968OB	128	50036AN	485
4523AI	188	4642BB	163	4669OB-OPAL	111	4851BC	229	4970BN	231	50036CM	485
4524AI	188	4650BN	118	4671BN	118	4851BN	227	4971BN	231	50036OZ	485
4525AI	188			4671OB	114	4852BC	229	4972BN	231	50037AN	485
4540RB	091			4671OB-CL	107	4852BN	227	4975BN	231	50037CM	485
4541RB	091	4650OB	114	4671OB-OPAL	110	4853BC	229	4978BN	230	50037OZ	485
4542RB	091		463			4853BN	227			50038AN	483
4543RB	091	4650OB-CL	107	4700		4855BC	229	5000		50038CM	483
4544RB	091	4650OB-OPAL	110	4717RB	034	4855BN	227	5000AN	502	50038OZ	483
4545RB	091		462	4720MC	093	4856BC	228	5000OB	503	50100CM	442
4546RB	091	4651BN	119		508	4856BN	226	5002AN	502	50102CM	442
4547RB	091	4651OB	115	4721MC	093	4858BC	229	5002OB	503	50103CM	442
4548RB	090	4651OB-CL	107		508	4858BN	227	5003AN	502	50104CM	442
4549RB	091	4651OB-OPAL	111	4724MC	093	4870BR	067	5003OB	503	5010BN	497
4561AT	121	4652BN	119	4725MC	093	4872BR	067	5004AN	502	5010CM	497
4563AT	121	4652OB	115	4727MC	093	4875BR	067	5004OB	503	5012BN	497
4564AT	121	4652OB-OPAL	111	4728MC	093	4876BR	067	50010CM	493	5012CM	497
4566AT	121	4653BN	117	4729MC	092	4878BR	066	50012CM	493	5013BN	497
4567AT	121	4653OB	113	4750SH	069	4880BB	146	50013CM	493	5013CM	497
4568AT	121	4653OB-OPAL	109	4752BC	069	4880PL	141	50014CM	493	5014BN	497
4569AT	120	4655BN	117	4754BC	069	4880PZ	143	50020AN	485	5014CM	497
4570KZ	217	4655OB	113	4756BC	068	4881BB	147	50020CM	485	50200CM	450
4571KZ	217	4655OB-CL	107	4770SH	149		515	50020OZ	485	50202CM	450
4572KZ	217	4655OB-OPAL	109	4771SL	149	4881CB	697	50021AN	484	50203CM	450
4574KZ	217	4656BN	117	4772SL	149	4881PL	141	50021CM	484	50204CM	450
4575KZ	217	4656OB	113	4774SL	149		514	50021OZ	484	5020BN	468
4576KZ	216	4656OB-CL	107	4775SL	149	4881PZ	144	50022AN	484	5020CM	467
4577KZ	217	4656OB-OPAL	109	4776SL	149	4885BB	147	50022CM	484	5020KZ	469
4590RY	131	4657BN	117	4778SL	149	4885PL	141	50022OZ	484	5022BN	468
4591RY	131	4657OB	113	4779SL	148	4885PZ	144	50023AN	485	5022CM	467
4594RY	131	4657OB-CL	106	4780OZ	257	4886BB	146	50023CM	485	5022KZ	469
4595RY	131	4657OB-OPAL	109	4780PL	259	4886PL	140	50023OZ	485	5023BN	468
4598RY	131	4659BN	116	4783OZ	257	4886PZ	143	50024AN	485	5023CM	467
4599RY	130	4659OB	112	4783PL	259	4887BB	146	50024CM	485	5023KZ	469
		4659OB-OPAL	108	4784OZ	257	4887PZ	143	50024OZ	485	5024BN	468
4600		4660BN	119	4784PL	259	4889BB	145	50025AN	485	5024CM	467
4620FB	169		461	4786OZ	257	4889PZ	142	50025CM	485	5024KZ	469
4622FB	169	4660OB	115	4786PL	259			50025OZ	485	5025BN	468
4626FB	168		463	4788OZ	257	4900		50026AN	485	5025CM	467
4630BN	081	4660OB-CL	107	4788PL	259	4900BN	123	50026CM	485	5025KZ	469
	504	4660OB-OPAL	111	4789OZ	256	4900EZ	126	50026OZ	485	5050BN	455
4630OB	505		462	4789PL	258	4933HB	245	50027AN	485	5050CM	454
4630OZ	083	4661BN	117	4790BN	123	4933PL	247	50027CM	485	5052BN	455
4630TB	085	4661OB	113	4790EZ	126	4935HB	244	50027OZ	485	5052CM	454
4631BN	081	4661OB-OPAL	109	4791BN	124	4935PL	246	50028AN	483	5053BN	455
	504	4662BN	118	4791EZ	127	4937HB	245	50028CM	483	5053CM	454
4631OZ	083	4662OB	114	4792BN	123	4937PL	247	50028OZ	483	5054BN	455
4631TB	085	4662OB-OPAL	110	4792EZ	126	4943TZ	189	50030AN	484	5054CM	454
4632BN	081	4663BN	118	4793BN	124	4946TZ	189	50030CM	484	50650BN	449
4632OZ	083	4663OB	114	4793EZ	127	4952HB	055	50030OZ	484	50652BN	449
4632TB	085	4663OB-CL	107	4794BN	124	4952LZ	057	50031AN	485	50653BN	449
4633BN	081	4663OB-OPAL	110	4794EZ	127	4952PL	059	50031CM	485	50654BN	449
4633OZ	083	4664BN	119								

5100

5100AN	470
5100BR	471
5100KZ	472
5102AN	470
5102BR	471
5102KZ	472
5103AN	470
5103BR	471
5103KZ	472
5104AN	470
5104BR	471
5104KZ	472
5105AN	470
5105BR	471
5105KZ	472
5122BK	159
51350BN	457
51352BN	457
51353BN	457
51354BN	457
51560BN	452
51562BN	452
51563BN	452
51564BN	452
5190CM	487
5191CM	487
5192CM	487
5193CM	487
5194CM	487

5200

5200BN	478
5202BN	478
5203BN	478
5204BN	478
5232BN	436
5232CM	437
5234BN	436
5234CM	437
5236BN	436
5236CM	437
52370BN	432
52372BN	432
52373BN	432
52374BN	432
52400BN	430
52402BN	430
52403BN	430
5250AN	459
5250CM	458
5251AN	459
5251CM	458
5252AN	459
5252CM	458
5253AN	459
5253CM	458
5254AN	459
5254CM	458
5255AN	459
5255CM	458
52700BN	453
52702BN	453

52703BN	453
52704BN	453

5300

53012BC	476
53012PN	477
53013BC	476
53013PN	477
53014BC	476
53014PN	477
5310BB	147
5310PL	141
5310PZ	144
5312BB	515
5312PL	514
5313BB	515
5313PL	514
5314BB	515
5314PL	514
5317BB	146
5317PL	141
5317PZ	143
53240BN	429
53241BN	429
53242BN	429
53243BN	429
53244BN	429
53320PL	486
53322PL	486
53323PL	486
53324PL	486
53350BN	443
53352BN	443
53353BN	443
53354BN	443
53550BN	447
53552BN	447
53553BN	447
53554BN	447
53580AN	488
53580OZ	489
53582AN	488
53582OZ	489
53583AN	488
53583OZ	489
53584AN	488
53584OZ	489
5362BN	504
5362OB	505
5363BN	504
5363OB	505
5370BN	460
5372BN	460
5373BN	460
5375BN	460
5390BB	511
5390PL	510
5391BB	511
5391PL	510
5392BB	511
5392PL	510
5393BB	511

5393PL	510
5394BB	511
5394PL	510

5400

54130BN	456
54132BN	456
54133BN	456
54134BN	456
5420CM	466
5421BN	436
5421BR	471
5421CM	466
5422CM	466
5423CM	466
5424CM	466
54260OB	507
54260PL	506
54261OB	507
54262OB	507
54262PL	506
54263OB	507
54263PL	506
54264OB	507
54264PL	506
5450AT	121

5500

55210BN	465
55210CM	464
55212BN	465
55212CM	464
55213BN	465
55213CM	464
55214BN	465
55214CM	464
5542OL	509
5543OL	509
5544OL	509
5545OL	509
55482BN	445
55482CM	444
55483BN	445
55483CM	444
55484BN	445
55484CM	444
5550BN	480
5550CM	479
5550KZ	481
5551BN	480
5551BR	495
5551CM	479
5552BN	480
5552CM	479
5552KZ	481
5553BN	480
5553CM	479
5553KZ	481
5554BN	480
5554CM	479
5554KZ	481
5555BN	480
5555CM	479
5555KZ	481

5556BN	480
5556CM	479
5556KZ	481
55750CM	451
55752CM	451
55753CM	451
55754CM	451
5580BB	513
5580PL	512
5582BB	513
5582PL	512
5583BB	513
5583PL	512
5584BB	513
5584PL	512
5585BB	513
5585PL	512
5590BN	234
5590CM	474
5592BN	475
5592CM	474
5593BN	475
5593CM	474
5594BN	475
5594CM	474

5600

5612BN	431
5613BN	431
5614BN	431
5615BN	431
56320AN	501
56322AN	501
56323AN	501
56422BN	446
56423BN	446
56424BN	446
5650BN	433
5650CM	434
5650OZ	435
5651BN	433
5651CM	434
5651OZ	435
5652BN	433
5652CM	434
5652OZ	435
5654BN	433
5654CM	434
5654OZ	435
5656BN	433
5656CM	434
5656OZ	435
56550BN	482
56552BN	482
56553BN	482
56554BN	482
5670OB	099
5680VZ	096
5692TB	473
5693TB	473

5700

5732MC	508
5733MC	508
5734MC	508
5740AN	498
5740BR	499
5742AN	498
5742BR	499
5743AN	498
5743BR	499
5744AN	498
5744BR	499
5770BN	448
5772BN	448
5773BN	448
5774BN	448

5800

5830AN	494
5830BR	495
5832AN	494
5832BR	495
5833AN	494
5833BR	495
5834AN	494
5834BR	495
5850BN	496
5850CM	496
5852BN	496
5852CM	496
5853BN	496
5853CM	496
5854BN	496
5854CM	496
5855BN	496
5855CM	496
58504BZ	745
58504LA	745
58504MZ	745
58504SW	745
58504TT	745
58506BZ	744
58506LA	744
58506SW	744
58506TT	744
58508BZ	745
58508LA	745
58508MZ	745
58508SW	745
58508TT	745
58780BN	491
58780CM	490
58780OZ	492
58782BN	491
58782CM	490
58782OZ	492
58783BN	491
58783CM	490
58783OZ	492
58784BN	491
58784CM	490
58784OZ	492
5892BN	461
5892OB	463

5892OB-OPAL	462
5893BN	461
5893OB	463
5893OB-OPAL	462
5894BN	461
5894OB	463
5894OB-OPAL	462
5895BN	461
5895OB	463
5895OB-OPAL	462

5900

5920BN	440
5920BR	441
5920CM	439
5922BN	440
5922BR	441
5922CM	439
5923BN	440
5923BR	441
5923CM	439
5924BN	440
5924BR	441
5924CM	439
5925BN	440
5925BR	441
5925CM	439

6600

6610BK	749
6611BK	749
6638BK	749
6660BK	749
6660BZ	749
6660OI	749
6661BK	749
6662BK	749
6663BK	749
6667BK	749
6680BK	749

6800

6808BK	749
--------	-----

8300

83667AN	418
83667BN	418
83667CM	418
83667OZ	418
83669AN	418
83669BN	418
83669CM	418
83669OZ	418

8400

8471SH	087
DSLG-40	007
DSLML-40	007

FR3000

FR30407BNI 416
 FR30407PBA 416
 FR30407PNI 416
 FR30824BNI 413
 FR30825BNI 413
 FR30826BNI 413
 FR30827BNI 413

FR3100

FR31434BLK 307
 FR31436BLK 306
 FR31437BLK 307
 FR31557BNI 417
 FR31557PCM 417

FR3200

FR32541ABR 327
 FR32542ABR 327
 FR32544ABR 327
 FR32545ABR 327
 FR32546ABR 326
 FR32547ABR 327
 FR32548ABR 327
 FR32557BLK 407
 FR32557CLD 406
 FR32557CRM 407
 FR32557TTM 407
 FR32557VBZ 407
 FR32903BKS 389
 FR32904BKS 389
 FR32905BKS 388
 FR32906BKS 389

FR3300

FR33507BNI 408
 418
 FR33507PCM 409
 418
 FR33730SLF 331
 FR33730VBZ 329
 FR33731SLF 331
 FR33731VBZ 329
 FR33732SLF 331
 FR33732VBZ 329
 FR33734SLF 331
 FR33734VBZ 329
 FR33735SLF 331
 FR33735VBZ 329
 FR33736SLF 330
 FR33736VBZ 328
 FR33737SLF 331
 FR33737VBZ 329

FR3400

FR34137BNI 411
 FR34774CLD 412
 FR34774TTM 412
 FR34774VBZ 412

FR3500

FR35002WAL 414
 FR35003WAL 414
 FR35004WAL 414

FR35007WAL 414
 FR35008WAL 414
 FR35009WAL 414
 FR35012WAL 415
 FR35013WAL 415
 FR35014WAL 415
 FR35017WAL 415
 FR35018WAL 415
 FR35019WAL 415

FR3600

FR36501ANG 403
 FR36501ANS 403
 FR36504ANG 403
 FR36504ANS 402

FR3700

FR37554BLK 404
 FR37554CLD 405
 FR37554PTR 405
 FR37554RBR 405

FR3800

FR38510BNI 410
 FR38510CLD 410
 FR38510PCM 410

FR4000

FR40200IRN 313
 FR40203IRN 313
 FR40204IRN 313
 FR40205IRN 313
 FR40206IRN 312
 FR40564IRN 323
 FR40566IRR 323
 FR40570IRR 323
 FR40572IRR 323
 FR40573IRR 322
 FR40574IRR 323
 FR40575IRR 322
 FR40576IRR 323
 FR40577IRR 322
 FR40578IRR 322
 FR40579IRR 321
 FR40703VIR 309
 FR40705VIR 308
 FR40707VIR 309
 FR40754BNI 391
 FR40754VBZ 391
 FR40756BNI 391
 FR40756VBZ 390
 FR40772SLF 345
 FR40774SLF 345
 FR40775SLF 345
 FR40776SLF 344

FR4100

FR41200IRR 319
 FR41202IRR 319
 FR41203IRR 319
 FR41204IRR 319
 FR41205IRR 319
 FR41206IRR 319
 FR41207IRR 319

FR41208IRR 318
 FR41240SH 315
 FR41240VBZ 315
 FR41242VBZ 315
 FR41246VBZ 315
 FR41248VBZ 314
 FR41430PAL 399
 FR41431PAL 399
 FR41433PAL 399
 FR41434PAL 398
 FR41435PAL 399
 FR41436PAL 399
 FR41437PAL 399
 FR41439PAL 399
 FR41611ORB 372
 FR41611SLF 375
 FR41612ORB 373
 FR41612SLF 376
 FR41613ORB 372
 FR41613SLF 375
 FR41614ORB 372
 FR41614SLF 375
 FR41616ORB 371
 FR41616SLF 374
 FR41617ORB 373
 FR41617SLF 376
 FR41622ORB 372
 FR41622SLF 375
 FR41624ORB 373
 FR41624SLF 376
 FR41627ORB 373
 FR41627SLF 376
 FR41941PAL 383
 FR41942PAL 383
 FR41946PAL 383
 FR41948PAL 383
 FR41949PAL 382

FR4200

FR42000SH 071
 337
 FR42002PNI 337
 FR42003PNI 337
 FR42006PNI 337
 FR42008PNI 336
 FR42280DIR 317
 FR42284DIR 317
 FR42286DIR 317
 FR42287DIR 317
 FR42288DIR 316
 FR42340PCM 379
 FR42341PCM 379
 FR42342PCM 379
 FR42343PCM 379
 FR42344PCM 378
 FR42347PCM 379
 FR42400BRC 370
 FR42401BRC 370
 FR42402BRC 370
 FR42404BRC 369
 FR42405BRC 369
 FR42406BRC 369
 FR42407BRC 370
 FR42408BRC 368

FR42500BME 367
 FR42504BME 367
 FR42506BME 367
 FR42508BME 366
 FR42720SLF 365
 FR42721SLF 365
 FR42724SLF 365
 FR42725SLF 365
 FR42728SLF 364
 FR42861VBZ 325
 FR42862VBZ 325
 FR42864VBZ 325
 FR42865VBZ 325
 FR42866VBZ 325
 FR42868VBZ 324

FR4300

FR43351PSS 339
 FR43352PSS 339
 FR43354PSS 339
 FR43355PSS 339
 FR43358PSS 338
 FR43359PSS 339
 FR43530PNI 335
 FR43531PNI 335
 FR43535PNI 335
 FR43536PNI 335
 FR43538PNI 334
 FR43620PNI 351
 FR43621PNI 351
 FR43622PNI 351
 FR43624PNI 351
 FR43625PNI 351
 FR43626PNI 351
 FR43628PNI 350
 FR43751SLF 353
 FR43752SLF 353
 FR43754SLF 353
 FR43758SLF 353
 FR43759SLF 352
 FR43910SLF 381
 FR43912SLF 381
 FR43913SLF 380
 FR43914SLF 381
 FR43916SLF 381
 FR43918SLF 381

FR4400

FR44100FRM 357
 FR44100SLF 359
 FR44102FRM 356
 FR44102SLF 359
 FR44103FRM 357
 FR44103SLF 359
 FR44104FRM 356
 FR44104SLF 359
 FR44105FRM 356
 FR44107FRM 355
 FR44107SLF 358
 FR44110FRM 357
 FR44110SLF 359
 FR44300BNI 333
 FR44304BNI 333
 FR44305BNI 333

FR44308BNI 332
 FR44413CLD 385
 FR44413PCM 385
 FR44413POG 385
 FR44500ANI 349
 FR44500BBZ 347
 FR44501ANI 349
 FR44501BBZ 347
 FR44502ANI 349
 FR44502BBZ 347
 FR44504ANI 349
 FR44504BBZ 347
 FR44505ANI 349
 FR44505BBZ 347
 FR44506ANI 349
 FR44506BBZ 347
 FR44508ANI 348
 FR44508BBZ 346
 FR44620BCH 362
 FR44621BCH 362
 FR44622BCH 361
 FR44623BCH 362
 FR44624BCH 361
 FR44625BCH 360
 FR44626BCH 362
 FR44627BCH 361

FR4500

FR45601BNI 341
 FR45601FBZ 343
 FR45602BNI 341
 FR45602FBZ 343
 FR45604BNI 341
 FR45604FBZ 343
 FR45606BNI 341
 FR45606FBZ 343
 FR45607BNI 341
 FR45607FBZ 343
 FR45608BNI 340
 FR45608FBZ 342
 FR45923BNI 393
 FR45923PNI 393
 FR45923VBZ 392

FR4600

FR46200BAM 401
 FR46204BAM 400
 FR46205BAM 401
 FR46206BAM 401

FR4700

FR47505PCM 397
 FR47506PCM 396
 FR47507PCM 397

FR4800

FR48430IRN 311
 FR48435IRN 311
 FR48436IRN 311
 FR48439IRN 310

FR4900

FR49190SLF 500
 FR49292PCM 387

WFR49293PCM 387
 FR49296PCM 387
 FR49298PCM 387
 FR49299PCM 386
 FR49450BNI 377
 FR49454BNI 377
 FR49458BNI 377

FR5200

FR52202ORB 373
 FR52202SLF 376

FR5500

FR55450PCM 428
 FR55452PCM 428
 FR55453PCM 428
 FR55454PCM 428

FR5600

FR56502BNI 395
 FR56503BNI 395
 FR56504BNI 395
 FR56505BNI 394
 FR56508BNI 395

FR5900

FR59192SLF 500
 FR59193SLF 500
 FR59194SLF 500

FR8800

FR88005GL 409
 418
 FR88009GL 409
 418
 FR88013GL 409
 418
 FR88021GL 409
 418
 FR88025GL 409
 418
 FR88033GL 409
 418
 FR88037GL 409
 418
 FR88101GL 408
 FR88105GL 409
 FR88504GL 418
 FR88508GL 418
 FR88512GL 418
 FR88516GL 418



*life*AGLOW®

THIS IS HINKLEY

At your fingertips | AWARD-WINNING CATALOGS

Check out our full range of products in easy-to-use, full color catalogs complete with sizing guidelines, design ideas and eco-tips.

Information 24/7/365 | DYNAMIC WEBSITE

hinkleylighting.com

Surf all of the details on our lighting collections, including the newest products from Hinkley and Fredrick Ramond, tips from professional designers and locate a Hinkley showroom in your area.

Make the world a better place | COMMUNITY INVOLVEMENT

The Hinkley Lighting family proudly supports breast cancer initiatives in an effort to help eradicate this horrible disease. By increasing awareness and supporting education and community events, together we can work towards finding a cure. Hinkley also supports a variety of other charitable organizations that strive to make a positive difference in the lives of others. Visit hinkleylighting.com for more information.

Be inspired | ENGAGING VIDEOS

youtube.com/hinkleylightinginc

Visit Hinkley on YouTube to watch our product, educational and brand videos.

Talk is chic | SOCIAL MEDIA

See what captivates us:

facebook.com/hinkleylighting

pinterest.com/hinkleylighting

houzz.com/hinkleylighting

instagram.com/hinkleylighting

twitter.com/hinkleylighting



Hinkley Lighting stands behind the quality of our lighting fixtures with product warranties that are among the strongest in the industry. For details of warranty coverage on specific products, please refer to hinkleylighting.com or consult a qualified Hinkley retail distributor.

Several Hinkley Lighting products are protected under U.S. Patent and foreign patent, or patent pending. For current information regarding Hinkley Lighting's patent portfolio, please visit hinkleylighting.com.

Consistent with our corporate strategy, we have printed this catalog using vegetable-based inks, paper made with wind power and FSC® certified paper which consists of 10% post-consumer recovered fiber.

According to the Mohawk Environmental Calculator, our paper selection preserves 309 trees for the future, saves 131,294 gallons of wastewater flow and prevents 28,603 lbs of greenhouse gases from being emitted into the atmosphere. Please consider joining our environmental efforts and recycling this catalog.

©2015 Hinkley Lighting, Inc.
All rights reserved in all copyrightable works.



Hinkley Lighting is a proud partner of the American Lighting Association.

HINKLEY

L I G H T I N G

CLASSIC, CHIC COLLECTIONS | HINKLEYLIGHTING.COM



FREDRICK RAMOND

ESTABLISHED 1965

HINKLEY'S LUXURY LINE | FREDRICKRAMOND.COM

33000 PIN OAK PARKWAY | AVON LAKE, OHIO 44012
PHONE (440) 653 5500 | FAX (440) 653 5555
SHOWROOM 3210 | DALLAS TRADE MART | DALLAS, TEXAS 75207

CATALOG 2015-2016 CAT15



\$25.00