

# 52" HUGGER FAN

52" indoor hugger fan with 5 reversible Cherry/Natural Cherry blades and a Brushed Nickel finish. With an 11-degree pitch, the hugger-style housing permits fan installation on lower ceilings. A powerful AirPro motor features a 3-speed, triple-capacitor control that can also be reversed to provide year-round comfort. Includes a 15-year warranty and is compatible with universal light kits. Also available with White blades and a White finish.

## FEATURES

- 15-year limited warranty
- Compatible with universal light kits
- Cannot be used with remote
- Add a P2630-30 wall control

## SIZE

52" dia., 8-1/8" ht.

## FINISHES

- Brushed Nickel - 09
- White - 30



### P2525-09

Brushed Nickel shown with Cherry Blades



### P2525-09


shown with P2610-09WB light kit\*  
Brushed Nickel shown with Cherry Blades



Natural Cherry



Cherry



### P2525-30

White shown with White Blades



White



White

## ENERGY INFORMATION AT HIGH SPEED

<b>AIRFLOW:</b>	3,229 cubic feet per minute
<b>ELECTRICITY USE:</b>	56 watts (excludes lights)
<b>AIRFLOW EFFICIENCY:</b>	58 cubic feet per minute per watt



Fan



Dry

Indoor only

\* Light kit sold separately.