

Knives & Cutting Tools

Klein provides a wide range of knives, scissors and other cutting tools for professional applications across all trades.

For Professionals...
Since 1857™



Pocket Knives – One Blade

Lightweight Pocket Knives

NEW!

- 440A stainless steel blade.
- Dual thumb studs for one-hand open.
- Pocket clip keeps knife readily available.
- Cat. No. 44201 features with 14-12 AWG solid and stranded wire stripping notches on backside of blade.
- Cat. Nos. 44144 and 44201 have liner locks to secure blade in open position and Cat. No. 44142 features the lock back to secure knife in open position.
- Cat. No. 44144 features silver aluminum handle for corrosion resistance and Cat. No. 44142 has a black aluminum handle for corrosion resistance.




44201



44144



44142



Cat. No. 44201 features stripping notches.

Cat. No.	Handle Type	Blade Length	Open Length	Weight (oz.)
Satin Finish Drop Point Blade				
44142	440A stainless steel	3-1/2" (89 mm)	6-3/4" (171 mm)	.14
44144	440A stainless steel	4" (60 mm)	8" (203 mm)	.28
44201	440A stainless steel	3-3/4" (95 mm)	8" (203 mm)	.31

Lightweight Lockback Knives

- Reversible thumb stud provides easy one-handed opening.
- Cat. Nos. 44003-44005 feature impact-resistant nylon resin handles with rubber insert.
- Cat. Nos. 44000, 44001, 44006 and 44007 have comfortable silver anodized-aluminum handles for corrosion-resistance.
- Cat. Nos. 44000-BLK and 44001-BLK have black chrome blade and black anodized-aluminum handle for corrosion-resistance.
- Cat. Nos. 44005R and 44005RC have a rounded tip for additional safety.



44001-BLK



44001



44005



44006



44007

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
Drop Point Blade				
44000	AUS 8 stainless steel	2-1/4" (57 mm)	3-1/8" (76 mm)	1.5
44000-BLK	AUS 8 stainless steel	2-1/4" (57 mm)	3-1/8" (76 mm)	1.1
44001*	AUS 8 stainless steel	2-1/2" (64 mm)	3-1/2" (89 mm)	2.5
44001-BLK*	AUS 8 stainless steel	2-1/2" (64 mm)	3-1/2" (89 mm)	1.3
44003	AUS 8 stainless steel	2-3/4" (70 mm)	4-1/8" (105 mm)	2.5
Sheepfoot Blade				
44004	AUS 8 stainless steel	2-3/8" (60 mm)	3-1/2" (89 mm)	1.5
44005	AUS 8 stainless steel	2-5/8" (67 mm)	4-1/8" (105 mm)	2.5
44006*	AUS 8 stainless steel	2-5/8" (67 mm)	3-1/2" (89 mm)	1.3
Coping Blade				
44007*	AUS 8 stainless steel	2-1/2" (63 mm)	3-1/2" (89 mm)	1.5
Rounded Tip Blade				
44005R	AUS 8 stainless steel	2-5/8" (67 mm)	4-1/8" (105 mm)	2.5
44005RC*	AUS 8 stainless steel	2-5/8" (67 mm)	4-1/8" (105 mm)	2.5

* Includes a pocket/belt clip.

All dimensions are in inches and (millimeters).



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury.

www.kleintools.com

See page 296 for additional information on warnings.

Pocket Knives – One Blade

Compact Pocket Knives – Drop-Point Blade

- Compact and lightweight knives.
- Stainless steel handle and blade for long life.
- Rosewood handle inserts on both sides.
- Modified spear point blade lockback open.

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
44032	stainless steel	1-5/8" (41 mm)	2-1/2" (64 mm)	1.0
44033	stainless steel	2" (51 mm)	3" (76 mm)	1.8
44034	stainless steel	2-5/8" (67 mm)	4" (102 mm)	4.0



44033

Sportsman Knives – Drop-Point Blade

- Curved handle with big bolster.
- Brass bolsters and ebony wood handle.
- Stainless steel blade for long life.
- Brass linings.
- Blade locks open.
- Cat. No. 44037 furnished with leather snap case with belt loop.

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
44036	stainless steel	2-3/8" (60 mm)	3-1/2" (89 mm)	2.5
44037	stainless steel	3-3/8" (86 mm)	4-7/8" (124 mm)	6.5



44037

Pocket Knife – Coping Blade

- Coping-type blade.
- Blade locks open.
- Compact and lightweight.
- Ideal for skinning small wire and cable.

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
1550-11	carbon steel	2-1/4" (57mm)	3-1/4" (83 mm)	1.5



1550-11

Pocket Knives – Sheepfoot Slitting Blade

- Extra-large curved sheepfoot slitting-blade – 2-5/8" (67 mm) long.
- Ideal for heavy-duty line work.
- Woodgrain plastic handle.
- Blade locks open.

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
1550-4	carbon steel	2-5/8" (67 mm)	4" (102 mm)	4.0
1550-44	stainless steel	2-5/8" (67 mm)	4" (102 mm)	4.0



1550-4

All dimensions are in inches and (millimeters).



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury.

www.kleintools.com

See page 296 for additional information on warnings.



Pocket Knives – One Blade

Pocket Knife – Slitting Blade

- Large, stainless steel, curved sheepfoot slitting blade – 2-1/2" (64 mm) long.
- Ideal for heavy-duty line work.
- Plastic handle.
- Blade locks open.

Cat. No.	Blade Steel	Blade Length	Length Closed	Weight (oz.)
1550-24	stainless steel	2-1/2" (64 mm)	4-3/8" (111 mm)	2.5



1550-24

2-Blade Pocket Knife – Spearpoint and Screwdriver-Tip Blades

- Standard spearpoint blade – 2-1/2" (64 mm) long.
- Screwdriver-tip blade – 2-1/2" (64 mm) long.
- Screwdriver-tip blade locks open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-2	carbon steel	2-1/2" (64 mm)	3-3/4" (95 mm)	4.0



1550-2

2-Blade Pocket Knife – Carbon Steel Sheepfoot and Insulation – Slitting Blade

- Curved sheepfoot skinning blade – 2-3/8" (60 mm) long.
- Special insulation-slitting blade – 1-1/2" (38 mm) long.
- Slitting blade locks open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-10	carbon steel	2-3/8" (60 mm) & 1-1/2" (38 mm)	3-3/4" (95 mm)	4.0



1550-10

Pocket Knives – Combination Blades

3-Blade Pocket Knife – Sheepfoot, Spearpoint and Screwdriver-Tip Blades

- Curved sheepfoot skinning blade – 2-3/8" (60 mm) long.
- Standard spearpoint blade – 2-1/2" (64 mm) long.
- Screwdriver-tip blade – 2-1/2" (64 mm) long.
- Screwdriver blade locks open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-6	carbon steel	2-3/8" (60 mm), 2-1/2" (64 mm), 2-1/2" (64 mm)	3-3/4" (95 mm)	5.0



1550-6

All dimensions are in inches and (millimeters).



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury.

www.kleintools.com

See page 296 for additional information on warnings.

Pocket Knives – Combination Blades

3-Blade Pocket Knife – Spearpoint, Insulation-Slitting and Screwdriver-Tip Blades

- Spearpoint blade – 2-1/2" (64 mm) long.
- Special insulation-slitting blade – 1-1/2" (38 mm) long.
- Screwdriver-tip blade – 2-1/2" (64 mm) long.
- Both slitting blade and screwdriver-tip blade lock open.

Cat. No.	Blade Steel	Blade Lengths	Length Closed	Weight (oz.)
1550-9	carbon steel	2-1/2" (64 mm), 1-1/2" (38 mm), 2-1/2" (64 mm)	3-3/4" (95 mm)	5.0



1550-9

Trip-Saver™ – Stainless Steel

- Unique multi-tool addresses the special needs of electricians and maintenance professionals while providing many other features handy on any job.
- Specially designed locking "L" handle snaps securely into the "L" channel, locking the fully opened blade or implement in place during use.
- Features the following:
Needle-Nose Pliers, Beveled Wire Cutter, Toothed Pipe Grippers, Files (coarse and fine), 5-Slot Wire Stripper (10-18) AWG, Wire-Looping Hole, Scraper, Awl/Reamer, Serrated Sheepsfoot Knife, Clip-Point Knife, Standard/Metric Ruler, Drywall Saw, Locking "L" Handle, #1 and #2 Phillips Hex Bits, Small-Slotted Hex Bit, Large-Slotted Hex Bit, 1/4" Socket Adapter, Lanyard Hole, Nylon Pouch.



1016

Cat. No.	Overall Length	Weight (lbs.)
1016	5-3/4" (143 mm)	.95

⚠️WARNING: Close handles to lock blade in place before use.

Sharpening Tools

Pocket-Sized Knife Sharpener



44151

- A rugged, versatile sharpener featuring fine craftsmanship and unique design.
- Sharpening rod unscrews and stores in handle for convenient carrying in tool box, pouch, or pocket.
- Sharpening rod is precision-cut, hard-chromed steel for accurate, consistent sharpening and long life.
- Magnetized to trap metal particles when sharpening.
- Handle is a high-visibility orange color with handy pocket clip.

Cat. No.	Blade Length	Length Closed	Weight (lbs.)
44151	3-3/4" (95 mm)	5-1/2" (140 mm)	.05


All dimensions are in inches and (millimeters).



⚠️WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury.

www.kleintools.com

See page 296 for additional information on warnings.



Sharpening Tools

Combination Knife and Scissors Sharpener

- High-grade, tungsten-carbide inserts sharpen both sides of the blade at the same time.
- Restores knife edge in three or four strokes.
- Built-in finger guard helps to protect your hand.
- Lightweight, compact size for easy carrying and storage.
- Sharpens electrician's scissors, pocket knives, retractable-blade utility knives, razor blade knives and serrated knives.



48036

Cat. No.	Overall Size	Weight (lbs.)
48036	4" L x 2-1/4" W x 3/4" D (102 mm x 57 mm x 19 mm)	.10

WARNING: Improper use of knife and scissors sharpener and/or failure to follow instructions can result in injuries. Keep your fingers behind the curved guard and your thumb securely on the multi-grooved thumb-rest indentation, never in front of it.

Utility Knives

Utility Knife – Retractable Blade

- Top button moves heavy-duty, razor-edged blade to any of three cutting positions.
- Double-ended, reversible blade retracts fully for carrying.
- Lightweight aluminum handle is shaped for comfort.
- Accepts most standard blades.
- Includes three standard blades, stored in handle.
- Made in the U.S.A.
- Leather holder available, Cat. No. 5185.



44100

Cat. No.	Length Closed	Weight (lbs.)
44100	6" (152 mm)	.22

Utility Knife Blade Dispenser

- 50 blades included.
- High-quality triple ground blades stay sharp longer.
- Gauge on dispenser indicates blades remaining.
- Convenient interim storage for used blades.
- Blades are compatible with all standard utility knives.




44103

Cat. No.	Dimensions	Weight
44103	4.33" x 2.80" x 1.30" (71 mm x 32 mm x 110 mm)	1 lb. (0.45 kg)

Utility Knife Blades

- Heavy-duty razor-edged blades.
- Universal size fits Klein and most other makes of utility knives.
- Blades are reversible for extra life.
- Blades made in the U.S.A.



44101

Cat. No.	Blade Size	Package Size	Weight (lbs.)
44101	2-7/16" x .025" (62 mm x 6 mm)	5 blades	.05

All dimensions are in inches and (millimeters).



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury.

www.kleintools.com

See page 296 for additional information on warnings.



Utility Knives

Camouflage Assisted-Open Folding Utility Knife

NEW!



44135

- Realtree Xtra® Camo design handle with rubber grip and TPR overmold looks good in the field and on the job site.
- Rugged, heavy-duty and durable construction.
- Spring-assisted opening with dual thumb knob for right- or left-handed use.
- Blade locks when in closed position.



Realtree-XTRA Camouflage Design © 2012 of Jordan Outdoor Enterprises, Ltd., all rights reserved.


Cat. No.	Length Closed	Overall Length w/Blade	Weight
44135	4.44" (113 mm)	7.0" (178 mm)	0.47 lbs. (0.21 kg)

Folding Utility Knife



44131


- Push button to easily open and close.
- Rugged, heavy-duty and durable construction.
- Contains a wire stripping notch.
- High quality, triple ground blades stay sharp longer.
- Rubber grips on handle for improved control and comfort.
- The bright orange handle color makes this knife easy to find in a tool bag or pouch.



Cat. No.	Length Closed	Overall Length w/Blade	Weight
44131	4.125" (104.8 mm)	6.375" (162 mm)	.27 lbs. (0.12 kg)

Self-Retracting Utility Knife

- Rugged, heavy-duty and durable construction.
- Knife incorporates a wire-stripping notch.
- Safety yellow handle for greater visibility.
- Blade removal/insertion without disassembly.



Cat. No.	Length Closed	Overall Length w/Blade	Weight
44136	5.0" (127 mm)	5.75" (146 mm)	0.44 lbs. (0.20 kg)

All dimensions are in inches and (millimeters).



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury.

Auto-Loading Folding Retractable Utility Knife



44130

- Rugged, heavy-duty and durable construction.
- Auto-loading blade for faster and safer blade changes.
- High quality triple ground blades stay sharp longer.
- Rubber grips on handle for improved control and comfort.
- Internal blade storage holds and includes 3 blades.
- Lock release to close knife.
- Equipped with belt clip.



Cat. No.	Length Closed	Overall Length w/Blade	Weight
44130	4.25" (108 mm)	6.625" (168.3 mm)	.47 lbs. (0.21 kg)

Klein Kurve™ Retractable Utility Knife



44133

- Rugged, heavy-duty and durable construction.
- Now with a wire-stripping notch.
- High quality, triple ground blades stay sharp longer.
- Rubber grips on handle for improved control and comfort.
- Designed for improved cutting ability.
- Internal blade storage includes and holds 6 blades.



Cat. No.	Length Closed	Overall Length w/Blade	Weight
44133	6.875" (175 mm)	7.0" (178 mm)	0.47 lbs. (0.21 kg)



44136

Blade retracts fully into housing when cut is complete.



Special-Purpose Knives

Cable-Sheath Splitting Knife



1515-S

- Compact, lightweight knife for opening lead cables.
- Rugged, forged tempered cutlery steel blade.
- Sharp, chisel-shaped edge.
- Hammer head on back.
- Plastic-dipped handle for comfort.
- Leather guard available, Cat. No. 5574S.

Cat. No.	Overall Length	Blade Length	Weight (lbs.)
1515-S	7-3/8" (187 mm)	2-19/32" (66 mm)	.35

Bell System Cable-Sheath Splitting Knife — Heavy-Duty



1515-1

- Heavy-duty knife for splitting cable sheaths.
- Rugged, forged tempered cutlery steel blade.
- Sharp chisel-shaped edge.
- Plastic-dipped handle for comfort.
- Leather guard available, Cat. No. 5574L.

Cat. No.	Overall Length	Blade Length	Weight (lbs.)
1515-1	8-3/4" (222 mm)	4-1/2" (114 mm)	1.20

Cable/Lineman's Skinning Knives



1570-3



1580-3

- Cat. Nos. 1570-3 and 1570-3LR feature three-inch steel blades that withstand frequent scoring and slitting of cable jacket.
- Notch on blade back for scraping or removing wire insulation.
- Comfortable textured handle with finger grooves and guard.
- No contact between stainless steel ring and hardened steel blade (Cat. No. 1570-3).
- Rectangle-shaped handle design for attachment to some utility hot stick equipment.
- Leather sheath available, Cat. No. 5163 only for Cat. Nos. 1570-3 and 1570-3LR.
- Cat. Nos 1580-3 has a 2" (51 mm) blade for increased control when scoring and slitting cable jacket and an ergonomic handle for maximum comfort.

Cat. No.	Description	Handle Color	Length Less Ring	Weight (lbs.)
1570-3	hook blade, notch, and ring	black	8" (203 mm)	.30
1570-3LR	hook blade and notch	black	8" (203 mm)	.29
1580-3	hook blade and notch	black	8" (203 mm)	.28 NEW!

Cable-Splicer's Knife



44200

- Special-purpose short blade with comfortable, full-sized, heavy-duty handle.
- Coping-type blade made of the finest cutlery steel, tough and carefully tempered to hold its edge.
- Handle is textured for comfort and firm grip.
- Hang hole for easy storage and portability.

Cat. No.	Overall Length	Blade Length	Weight (lbs.)
44200	6-1/4" (159 mm)	1-3/4" (44 mm)	.15

Cable-Splicer's Kits



46037

- Cuts cable, telephone wire, and strips insulation.
- Dimensions: 2-1/8" x 7-1/2" (54 mm x 191 mm).

Cat. No.	Kit Contains	Weight (lbs.)
46037	cable splicer's kit	.50
Cat. No.	Description	
44200	cable-splicer's knife	
2100-7	electrician's scissors with stripping notches	
5187	slotted leather holder for belts up to 2" (51 mm) wide	



46039

Cat. No.	Kit Contains	Weight (lbs.)
46039	cable splicer's kit - with free-fall snip	.58
Cat. No.	Description	
44200	cable-splicer's knife	
2101-0	free-fall snip	
5187	slotted leather holder for belts up to 2" (51 mm) wide	

All dimensions are in inches and (millimeters).



Electrician's Scissors

Electrician's Scissors



2100-5

- Designed for telecom and electrical applications and heavy-duty use.
- Strong, tough tempered steel.
- Nickel-plated finish resists corrosion.
- Scraper and file on outside of both blades.

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
2100-5	5-1/4" (133 mm)	1-7/8" (48 mm)	.20

Electrician's Scissors – Stripping Notches



2100-7

- Upper blade has notches for stripping 19 AWG and 23 AWG wire.
- Designed for telecom and electrical applications and heavy-duty use.
- Strong, tough tempered steel.
- Nickel-plated finish resists corrosion.
- Scraper and file on outside of both blades.
- Serrated, lower blade reduces slippage.

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
2100-7	5-1/4" (133 mm)	1-7/8" (48 mm)	.20

Stainless Steel Electrician's Scissors – Stripping Notches



2100-9



2100-8

- Stainless steel blades to maintain blade durability and sharpness.
- Blade is fully serrated for non-slip cutting action.
- Cat. No 2100-8 features a free-fall snip feature for ease of use.
- Cuts electrical communication 19 AWG and 23 AWG wire.
- Cat. No 2100-8 has an extended handle to provide comfort and cutting leverage for wire cutting application.

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
2100-8	6-5/16" (160 mm)	1-7/8" (48 mm)	.21
2100-9	5-1/4" (133 mm)	1-7/8" (48 mm)	.21

Industrial High-Leverage Shears

High-Leverage Snip



22000

- Nickel chrome plating resists corrosion and rusting.
- Cat. Nos. 22001 and 22002 have broad, short jaws provide powerful cutting action.
- Cat. Nos. 22001 and 22002 feature one serrated blade for non-slip cutting action.
- Cat. Nos. 22002 and 22003 have extended handles to provide comfort and cutting leverage.
- Cat. Nos. 22000 and 22003 are high-leverage to provide powerful cutting action for light metals, rubber and heavy fabrics.
- Cat. No. 22001 cuts light wire, fabric, cable and cordage.
- Cat. No. 22002 cuts rubber, cables, light metal, wire metal screens, cordage, plastics and ropes.

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
22000	7" (180 mm)	1-3/4" (45 mm)	.34
22001	8" (203 mm)	2" (51 mm)	.55
22002	8-1/2" (216 mm)	2" (51 mm)	.55
22003	9" (229 mm)	3" (76 mm)	.49

Large Broad Blade Utility Shear



22002

Broad Blade Utility Shear



22001

8" High-Leverage Utility Shear




22003

All dimensions are in inches and (millimeters).



www.kleintools.com

See page 296 for additional information on warnings.



Industrial Utility Snips

High-Leverage Kevlar® Snip



24000


- Nickel chrome plating resists corrosion and rusting.
- One blade is serrated for non-slip cutting action.
- Spring loaded for self-opening action.
- Cat. Nos. 24000 and 24001 includes a handy closure lock for convenient storage.
- Compatible for right- and left-handed users.
- Cat. Nos. 24000, 24001 are excellent for cutting Kevlar® insulation in fiber optic applications
- Cat. No. 24005 is excellent for cutting electronics and filaments.

Spring Action Snip



24001

5" Electronic Filament Snip



24005

Kevlar® is a registered trademark of E.I. du Pont de Nemours and Company.

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
24000	6-1/2" (165 mm)	5/8" (16 mm)	.28
24001	6-1/2" (165 mm)	1" (25 mm)	.28
24005	5" (127 mm)	1" (25 mm)	.22

Bent Trimmers

8" Bent Trimmer

- Cuts plastic, rubber, rubber roofing, roofing materials, cording, vinyl, fiberglass components and cloth materials.



23008

Features:

- Nickel-chrome plating resists corrosion and rusting.
- Extended handle provides comfort and cutting leverage.



23010

10" Bent Trimmer

- Cuts plastic, rubber, rubber roofing, roofing materials, cording, vinyl, fiberglass insulation and cloth materials.



23011

11-1/4" Bent Trimmer

- Cuts felt lining, muslin, cord, rubber, abrasive materials and multiple layers of fabric.



Single Serrated Blunt Blade Shear

23015

- Cuts belting, abrasive belting, heavy fabric, leather, upholstery and heavy carpet.
- Deep serrated blade for non-slip cutting action.

Cat. No.	Overall Length	Cutting Length	Weight (lbs.)
23008	9" (229 mm)	3-1/2" (89 mm)	.41
23010	10-1/2" (267 mm)	4-1/2" (114 mm)	.99
23011	11-1/4" (286 mm)	4-3/4" (121 mm)	1.24
23015	9-3/4" (248 mm)	3-3/16" (81 mm)	.94

All dimensions are in inches and (millimeters).

