



**MOBERN**  
LIGHTING

# LED Buyer's Guide



# ALWAYS ON.

# About Mobern

Our philosophy is simple: your success is our success. It's why our customers call us a hidden gem in the lighting industry. Expect a relationship, with fair pricing and reliable service you can pass along to your clients.

NO SMOKING


## Cutting Edge From The Start

The year is 1939, and fluorescent lighting is introduced for the first time at the New York World's Fair. Just five years later, Hyman Bernstein and Nathan Movitz combine their talents, and their last names, to create Mobern Lighting - one of the first fluorescent lighting manufacturers in the world. Seventy-five years later, technology has changed, but Mobern's responsive service, fair pricing, and expert staff has remained constant.



## Helping Your Business Shine

Today, Mobern's 80,000 square foot state-of-the-art factory and showroom houses the stock and resources of an industry giant - but our friendly, knowledgeable team has the same family-owned feel that we were built on in 1944. With 75 years of experience, you can bet our team has the answers to even the most complex lighting problems. Let's work together to make your business shine.



## Table of Contents

Controls	4
Acoustic	6
Custom Fixtures	8
High Bays	9
Smart Strips	15
Strips	16
Linear Pendant	20
Surface	35
Decorative Surface	40
Linear Wall	41
Recessed Linear	46
Recessed	52
Undercabinet	58
Retrofit	59
LED CTC	62
Enclosure	65
Outdoor	67
Exit Sign	83
Combos	85
Emergency	87
Remote Head	89
Inverters	90
EZLED	92
SaveGreen Tubes	108

*Together,  
the future  
is bright.*

# CONTROLS

Let Mobern be your integrated fixture control supplier! We have the ability to work with any controls manufacturer to seamlessly integrate the controls you need. We offer different types of sensors including remote-mounted or integrated sensors ranging from on/off to connected/dimming/time of day controls sensors. Our connected control protocols can be used to create scenes, zones, and custom dimming. All of this handled conveniently by your smart device or wall switch.



Sensor	Occupancy	Daylight Harvesting	Person Control	Color Tuning	Continuous Dimming	User Interface	Energy Monitor	Remote Diagnostics	External Integration	Wet Location	Standard vs. High Bay
OS (Basic)	Y									O	O
OSD	Y	Y			Y					O	
OSW	Y									Y	
OSWD	Y	Y			Y					Y	
SS	Y									O	
SSM	Y	Yes, on/off									
SSD	Y	Y			Y						
McWong Mesh	Y	Y	Y	Y	Y	Y				O	O
Ultrasonic Occupancy	Y									O	O
Ceiling Mount	Y	O								O	
Easy Sense	Y	Y	Y		Y	Y	Y	Y	Y w/ Zigbee Controls	O	
Enlighted Sensor	Y	Y	Y	Y	Y	Y					
Sensilum	Y	Y	Y		Y		Y		Y w/ DEXAL		Y

Y - Yes

O - Optional



OS



OSD



OSW



OSWD



SS/SSD



SSM



McWong Mesh Sensors



Ultrasonic Occupancy



Ceiling Mount



Easy Sense



Enlighted Sensor



Sensilum



# CONTROLS

## Control Protocols

Wired	
DALI	Flexible system with possibility to create separate lighting groups with easy wiring / Special knowledge is required for software commissioning
DMX	System specifically suited for dynamic (color) lighting. EX: stage lighting in theatres or architectural lighting
0-10V	Low cost, simple system / Good for integration with sensors
Wireless	
RF	Great for room-to-room setup and room programming / Shorter range / Programmable scenes available on controllers
Zigbee	Zigbee systems can easily do anything from room-to-room programming all the way to advanced systems controls for homes and offices
Wifi	Wifi is easily accessible from a smart phone and can be controlled from anywhere in the world if set up properly
Bluetooth	Bluetooth can control a single fixture or be built into a mesh network that can control a whole building

For single room or single fixture control, use:

- ▶ 0-10V
- ▶ RF
- ▶ Zigbee
- ▶ Bluetooth



*Continuous Dimming  
& 1 Set Scene*



*Step Dim Controller*

For full system integration, building control, or floor-by-floor control, use:

- ▶ DALI
- ▶ DMX
- ▶ Zigbee
- ▶ Wifi
- ▶ Bluetooth

If you are interested in a fully integrated system, or are unsure of what you are looking for, please call Mobern for assistance.



*Step Dim Controller*



*Control Via Smart Device*

# ACOUSTIC

A light fixture that does more for your space



This highly customizable fixture seamlessly integrates quality lighting with sound absorbing technology. It is functional as a stand alone fixture or as part of a matching baffle system. With four different length options, three different height options, twenty-four different finishes, and three different end styles, the creative possibilities are endless for your unique space.

## ABL3-LED

### Acoustical Baffle Light

- ▶ Designed to optimize sound absorption
- ▶ Sound absorbing material
- ▶ Available in multiple lengths and heights
- ▶  $L_{70} > 50,000$  hrs.
- ▶ Min CRI 80



### Acoustic Baffle Light

PART NUMBER	DESCRIPTION
ABL3-12P24LED13DDMV07BSF40H6W5	24"L x 3"W x 12"H / 13W 1,300L / White Fabric Finish / Type A End Style / Frosted Lens / 4000K
ABL3-12P24LED23DDMV07BSF40H6W5	24"L x 3"W x 12"H / 23W 2,300L / White Fabric Finish / Type A End Style / Frosted Lens / 4000K
ABL3-12P48LED26DDMV07BSF40H6W5	48"L x 3"W x 12"H / 26W 2,600L / White Fabric Finish / Type A End Style / Frosted Lens / 4000K
ABL3-12P48-LED45DDMV07BSF40H6W5	48"L x 3"W x 12"H / 45W 4,500L / White Fabric Finish / Type A End Style / Frosted Lens / 4000K
ABL3-12P72LED39DDMV07BSF40H6W5	72"L x 3"W x 12"H / 39W 3,900L / White Fabric Finish / Type A End Style / Frosted Lens / 4000K
ABL3-12P72LED68DDMV07BSF40H6W5	72"L x 3"W x 12"H / 68W 6,800L / White Fabric Finish / Type A End Style / Frosted Lens / 4000K
ABL3-12P96LED52DDMV07BSF40H6W5	96"L x 3"W x 12"H / 52W 5,200L / White Fabric Finish / Type A End Style / Frosted Lens / 4000K
ABL3-12P96LED90DDMV07BSF40H6W5	96"L x 3"W x 12"H / 90W 9,000L / White Fabric Finish / Type A End Style / Frosted Lens / 4000K

Also available in 30K, 35K, & 50K.


# ACOUSTIC



## END CAP OPTIONS:



## END CAP FINISHES:



## FABRIC COLOR OPTIONS:



# CUSTOM FIXTURES



**Y44-LED**  
4"x4" Linear "Y"


Whether you need to simply meet specifications or tackle a complex lighting problem, our team of lighting specialists have the knowledge to help you find an answer. We can customize our vast selection of fixtures with controls, wattage/lumen packages, finish options, and more to meet your specific application requirements. From our first conversation to product delivery, our service solutions will help you make the smartest choice for your lighting!



**CALL FOR  
CUSTOM  
PRICING!**



**HX44-LED**  
4"x4" Linear Hexagon



**FMS-FP**  
Flex Mounting System  
For Flat Panel



**RKITB-LED**  
Custom Retail  
Recessed Retrofit Kit



**CF-LED**  
Window Fixture

# LIGHTING SOLVED.





# High Bays

Evolution  
of the  
High Bay  
(from HID  
to LED)



**HID**



**FLUORESCENT**



**LED**

<b>ENERGY</b>	455 Watts	350 Watts	195 Watts
<b>LUMEN OUTPUT</b>	36,000 Lumens	29,100 Lumens	30,000 Lumens
<b>LIFE</b>	20,000 Hours	30,000 Hours	50,000 Hours
<b>MAINTENANCE</b>	Re-Lamp & Re-Ballast	Re-Lamp & Re-Ballast	Replace Driver

# HIGH BAYS

## LED Premium High Bay (Optional Lens)

The HBPA precision-formed reflector system creates ideal output for warehouses, manufacturing plants, sports facilities, and retail spaces.



Shown with FR lens

ITEM NO.	DESCRIPTION
HBPA-24LED80DMV50	23.379"L x 15.575"W x 4.296"H / 80W 10,000L / 5000K
HBPA-24LED122DMV50	23.379"L x 15.575"W x 4.296"H / 122W 15,000L / 5000K
HBPA-48LED80DMV50	45.160"L x 15.575"W x 4.296"H / 80W 10,000L / 5000K
HBPA48-LED122DMV50	45.160"L x 15.575"W x 4.296"H / 122W 15,000L / 5000K
HBPA-48LED149DMV50	45.160"L x 15.575"W x 4.296"H / 149W 21,150L / 5000K
HBPA-48LED175DMV50	45.160"L x 15.575"W x 4.296"H / 175W 25,050L / 5000K
HBPA48-LED215DMV50	45.160"L x 15.575"W x 4.296"H / 215W 31,380L / 5000K
HBPA-48LED260DMV50	45.160"L x 15.575"W x 4.296"H / 220W 33,000L / 5000K
HBPA-48LED280DMV50	45.160"L x 15.575"W x 4.296"H / 280W 41,120L / 5000K
HBPA-48LED315DMV50	45.160"L x 15.575"W x 4.296"H / 315W 45,440L / 5000K
HBPA-48LED355DMV50	45.160"L x 15.575"W x 4.296"H / 355W 50,119L / 5000K

Add "FR" or "CL" after "DMV" for frosted or clear lens. For occupancy sensor, wireguard, or emergency, add "OS", "WG", or "EM" to the end of the part number. Consult for up & downlight options. Also available in 30K, 35K, & 40K.

## LED Industrial Open Frame High Bay

Available with uplight & downlight configurations with full specular mirrored reflectors, this unit is an ideal warehouse fixture. Lens optics are adjustable up to 15%.




Shown with FR lens

ITEM NO.	DESCRIPTION
HBIA-24LED75DMV50	24.22"L x 12.74"W / 2 rows 75W 10,500L / 5000K
HBIA-24LED89DMV50	24.22"L x 12.74"W / 2 rows 89W 12,000L / 5000K
HBIA-24LED132DMV50	24.22"L x 19.87"W / 4 rows 132W 19,000L / 5000K
HBIA-24LED175DMV50	24.22"L x 19.87"W / 4 rows 175W 24,000L / 5000K
HBIA-48LED104DMV50	46.26"L x 12.74"W / 2 rows 104W 15,000L / 5000K
HBIA-48LED132DMV50	46.26"L x 12.74"W / 2 rows 132W 19,000L / 5000K
HBIA-48LED175DMV50	46.26"L x 12.74"W / 2 rows 175W 24,000L / 5000K
HBIA-48LED215DMV50	46.26"L x 19.87"W / 4 rows 215W 32,000L / 5000K
HBIA-48LED280DMV50	46.26"L x 19.87"W / 4 rows 280W 40,000L / 5000K
HBIA-48LED355DMV50	46.26"L x 19.87"W / 4 rows 355W 49,000L / 5000K

Add "FR" after "DMV" for frosted lens. Replace "DMV" with "DHV" for 347-480VAC. For occupancy sensor or emergency add "OS" or "EM" to the end of the part number. Add "SS" to the end of part number for integrated sensor. Consult for higher wattage and lumen output options. Also available in 30K, 35K, & 40K.



Shown with integrated sensor



Custom color options available!

## In-House Photometric Lab

Mobern has a photometric lab to produce IES files for our products. Consult if you need a special photometric done on a fixture or a lighting layout.





# HIGH BAYS

## LED Premium High Bay

The LHBIP precision-formed reflector system creates ideal output for warehouses, manufacturing plants, sports facilities, and retail spaces.



ITEM NO.	DESCRIPTION
----------	-------------

LHBIP-LED110MV50K	21.5"L x 11.8"W x 2.0"H / 110W 14,680L / 5000K
LHBIP-LED170MV50K	21.5"L x 16.0"W x 2.0"H / 170W 22,020L / 5000K
LHBIP-LED230MV50K	43.0"L x 11.8"W x 2.0"H / 220W 29,370L / 5000K

For occupancy sensor, add "OS" at the end of the part number. Consult factory for emergency options. Fixtures include chain mounting kits. Consult for different wattages and higher lumens. Also available in 40K.



## High Output Premium LED High Bay

ITEM NO.	DESCRIPTION
----------	-------------

LHBIP-LED240DMV50	43"L x 20"W x 1.5"H / 240W 33,380L / 5000K
LHBIP-LED320DMV50	43"L x 20"W x 1.5"H / 320W 45,500L / 5000K

Consult for 200W option. Also available in 30K, 35K, & 40K.

## Accessories (Fine tune your high bay for your application)

ITEM NO.	DESCRIPTION
----------	-------------

### 110W Accessories

FL-LHB1x2-MW	1x2 High Bay Door Frame Set w/ Matte White Lens
A-LHB1x2-WG	1x2 Wire Guard White
A-LHBIFMK	Flush Mounting Kit 6"L x 2"W x 0.8"H
A-LHBIPMK	Pendant Mounting Kit 3.4"L x 2.3"W x 2"H

### 170W Accessories

FL-LHB2x2-MW	2x2 High Bay Door Frame Set w/ Matte White Lens
A-LHB2x2WG	2x2 Wire Guard White
A-LHBIFMK	Flush Mounting Kit 6"L x 2"W x 0.8"H
A-LHBIPMK	Pendant Mounting Kit 3.4"L x 2.3"W x 2"H

### 230W Accessories

FL-LHB2x4-MW	2x4 High Bay Door Frame Set w/ Matte White Lens
FL-LHB2x4-WG	2x4 Wire Guard White
A-LHBIFMK	Flush Mounting Kit 6"L x 2"W x 0.8"H
A-LHBIPMK	Pendant Mounting Kit 3.4"L x 2.3"W x 2"H

### 240W and 320W Accessories


A-LHBIPMK-HO	Pendant Mounting Kit for LHBIP High Output LED High Bay
--------------	---



Shown with pendant mounting kit



# HIGH BAYS



## LED Premium High Bay Our most popular style!

The FHBC precision-formed reflector system creates ideal output for warehouses, manufacturing plants, sports facilities, and retail spaces.

ITEM NO.	DESCRIPTION
FHBC-48LED114DMV50	48"L x 16"W x 3.6"H / 114W 17,560L / 5000K
FHBC-48LED144DMV50	48"L x 16"W x 3.6"H / 144W 21,305L / 5000K
FHBC-48LED166DMV50	48"L x 16"W x 3.6"H / 166W 25,150L / 5000K
FHBC-48LED195DMV50	48"L x 16"W x 3.6"H / 195W 28,410L / 5000K
FHBC-48LED272DMV50	48"L x 16"W x 3.6"H / 272W 36,000L / 5000K

Some options and accessories shown below. Consult factory for other wattage and lumen packages.

## Low Bay

Same great workhorse with lower output for low ceiling applications.

ITEM NO.	DESCRIPTION
FHBC-48LED97DMV40	48"L x 16"W x 3.6"H / 97W 13,795L / 5000K

## Mini High Bay

Ideal for low to medium ceiling applications in warehouses, manufacturing plants, sports facilities, and retail spaces.

ITEM NO.	DESCRIPTION
FHBC-24LED57DMV50	24"L x 16"W x 3.6"H / 57W 7,640L / 5000K
FHBC-24LED114DMV50	24"L x 16"W x 3.6"H / 114W 16,000L / 5000K
FHBC-24LED144DMV50	24"L x 16"W x 3.6"H / 144W 19,000L / 5000K

Shown with door frame lens



ITEM NO.	DESCRIPTION
<b>Lens Options</b>	
L1080	FHBC Lens Wraparound for 48"L x 16"W Body / Clear
L1080-FR	FHBC Lens Wraparound for 48"L x 16"W Body / Frosted

ITEM NO.	DESCRIPTION
<b>High Bay Accessories</b>	
OS	External Mounted Occupancy Sensor
WG	Wire Guard for FHBC 16"
AC120-TOGGLE-2PK	Gripple Style Cable Kit
A144-XX	Chain Kit - 4 "V" Hooks & Chain Included
EM	Emergency Driver
A-FHBC7	Center Hub for 3/4" Pipe



Add "WG" to the end of the part number for optional wire guard.  
\*Cannot be used with door frame\*



# HIGH BAYS

## LED High Bay Baffle

This specially-designed baffle reduces glare, making it ideal for retail applications.



ITEM NO.	DESCRIPTION
FHBR-48LED32DMV50	48.0"L x 11.25"W x 4.25"H / 32W 3,450L / 5000K
FHBR-48LED48DMV50	48.0"L x 11.25"W x 4.25"H / 48W 5,640L / 5000K
FHBR-48LED57DMV50	48.0"L x 11.25"W x 4.25"H / 57W 6,400L / 5000K
FHBR-48LED72DMV50	48.0"L x 11.25"W x 4.25"H / 72W 8,200L / 5000K
FHBR-96LED97DMV50	96.0"L x 11.25"W x 4.25"H / 97W 11,300L / 5000K
FHBR-96LED114DMV50	96.0"L x 11.25"W x 4.25"H / 114W 19,500L / 5000K

Also available in 30K, 35K, & 40K.

## LED Full Body High Bay With Lens

This lensed high bay reduces glare, making it ideal for retail applications.



ITEM NO.	DESCRIPTION
FHBX-48LED32DMVFR50	48.0"L x 11.25"W x 4.25"H / 32W 3,450L / Frosted Lens / 5000K
FHBX-48LED48DMVFR50	48.0"L x 11.25"W x 4.25"H / 48W 5,640L / Frosted Lens / 5000K
FHBX-48LED57DMVFR50	48.0"L x 11.25"W x 4.25"H / 57W 6,400L / Frosted Lens / 5000K
FHBX-48LED72DMVFR50	48.0"L x 11.25"W x 4.25"H / 72W 8,200L / Frosted Lens / 5000K
FHBX-96LED97DMVFR50	96.0"L x 11.25"W x 4.25"H / 97W 11,300L / Frosted Lens / 5000K
FHBX-96LED114DMVFR50	96.0"L x 11.25"W x 4.25"H / 114W 19,500L / Frosted Lens / 5000K

Also available in 30K, 35K, & 40K.

## Round Sensor-Ready High Bay

This round high bay easily replaces most HID, induction, and fluorescent high bay fixtures.



ITEM NO.	DESCRIPTION
HBRMSR-LED135DMVBZ50	15.35"Dia x 9.16"H / 135W 19,400L / Dark Bronze Finish / 5000K
HBRMSR-LED175DMVBZ50	15.35"Dia x 9.16"H / 175W 25,600L / Dark Bronze Finish / 5000K
HBRMSR-LED200DMVBZ50	15.35"Dia x 9.16"H / 200W 29,800L / Dark Bronze Finish / 5000K

Also available in 40K. Add "OS" for motion sensor. Add "EM" for emergency battery backup.

ITEM NO.	DESCRIPTION
<b>High Bay Accessories</b>	
REF-HBRM-CL-KIT	Clear Acrylic Reflector & 4 Stainless Steel Screws
REF-HBRM-FR-KIT	Frosted Acrylic Reflector & Stainless Steel Screws
A-S16-CB	16" Stainless Steel Clamp Band (Required When Using Lens)
L-CDL16-FR*	16" Frosted Acrylic Conical Drop Lens
L-CDL16-CL*	16" Clear Acrylic Conical Drop Lens
L-SFL16-FR*	16" Frosted Acrylic Smooth Flat Lens
L-SFL16-CL*	16" Clear Acrylic Smooth Flat Lens

\*Must purchase A-S16-CB with lens.



Clear Acrylic



Frosted Acrylic



Optional motion sensor for HBRMSR-LED




Emergency backup for HBRMSR-LED (mounts to top of fixture)

# WET LOCATION HIGH BAYS



## Wet Location Vapor Tight High Bay

Demanding environments such as cold storage, warehouses, parking garages, commercial kitchens, and car washes call for this tough, enclosed, gasketed high bay.



### ITEM NO.

### DESCRIPTION

ITEM NO.	DESCRIPTION
VWFHB-LED80DMVCL50	51.91"L x 14.61"W x 5.95"H / 80W 8,730L / Clear Lens With Frosted Ends / 5000K
VWFHB-LED100DMVCL50	51.91"L x 14.61"W x 5.95"H / 100W 11,100L / Clear Lens With Frosted Ends / 5000K
VWFHB-LED120DMVCL50	51.91"L x 14.61"W x 5.95"H / 120W 13,350L / Clear Lens With Frosted Ends / 5000K
VWFHB-LED140DMVCL50	51.91"L x 14.61"W x 5.95"H / 140W 15,550L / Clear Lens With Frosted Ends / 5000K
VWFHB-LED150DMVCL50	51.91"L x 14.61"W x 5.95"H / 150W 16,500L / Clear Lens With Frosted Ends / 5000K
VWFHB-LED180DMVCL50	51.91"L x 14.61"W x 5.95"H / 180W 20,000L / Clear Lens With Frosted Ends / 5000K

For emergency, add "EM". Change "CL" to "FR" for Frosted Lens. See specification sheet for a full list of mounting options and accessories. Also available in 30K, 35K, & 40K.



## Wet Location Vapor Tight Low Bay

This low bay version of the fixture above provides the same tough environment characteristics with a lower output.

### ITEM NO.

### DESCRIPTION

ITEM NO.	DESCRIPTION
VWHBS-LED80DMV50	26.6"L x 14.5"W x 5.8"H / 80W 8,000L / Clear Lens With Frosted Ends / 5000K
VWHBS-LED100DMV50	26.6"L x 14.5"W x 5.8"H / 100W 10,000L / Clear Lens With Frosted Ends / 5000K
VWHBS-LED140DMV50	26.6"L x 14.5"W x 5.8"H / 140W 14,000L / Clear Lens With Frosted Ends / 5000K


For emergency, add "EM". Change "CL" to "FR" for Frosted Lens. See specification sheet for a full list of mounting options and accessories. Also available in 30K, 35K, & 40K.




Frosted Lens

## Hanging Accessories:

V-Hook Bracket  
(Sold Individually)



Surface Mount Bracket  
(Sold Individually)



▶ **H137** - V-Hook Bracket\*


\*Order 2 brackets per fixture

▶ **VWFHB-MBCM** - Surface Mount Bracket. Mounts 1.25" From Ceiling\*

\*Order 2 brackets per fixture



# SMART STRIPS



## Linear Fixture With Sensor

Make a bold statement with this 3.25"W strip that can be surface or pendant mounted individually or in continuous runs.

ITEM NO.	DESCRIPTION
LD23-24LED20DMVWHFR40SS	23.60"L x 2.38"W x 3.25"H / 20W 2,000L / White Finish / Frosted Lens / 4000K
LD23-48LED31DMVWHFR40SS	47.25"L x 2.38"W x 3.25"H / 31W 3,200L / White Finish / Frosted Lens / 4000K
LD23-96LED62DMVWHFR40SS	94.43"L x 2.38"W x 3.25"H / 62W 6,200L / White Finish / Frosted Lens / 4000K

Step dimming driver (SDMV) turns fixture on when occupied and dims to 50% when not. Consult for other finishes. Available with pendant mount in 30K, 35K, & 50K. See pages 4 & 5 for more sensor options.



Daylight harvesting sensor

## LED Linear Fixture With Daylight Harvesting Sensor

The SSD daylight harvesting sensor in conjunction with the 0-10V driver (DMV) allows the light level to adjust to ambient light.

ITEM NO.	DESCRIPTION
LD23-24LED20DMVWHFR40SSD	23.0"L x 2.38"W x 3.25"H / 20W 2,000L / White Finish / Frosted Lens / 4000K
LD23-48LED31DMVWHFR40SSD	47.25"L x 2.38"W x 3.25"H / 31W 3,200L / White Finish / Frosted Lens / 4000K
LD23-96LED62DMVWHFR40SSD	94.43"L x 2.38"W x 3.25"H / 62W 6,200L / White Finish / Frosted Lens / 4000K

Also available in 30, 35, & 50K.

## Wide Body Linear Strip With Sensor

This 3" wide linear strip makes a bold statement with a minimalistic design and a built-in occupancy sensor.

ITEM NO.	DESCRIPTION
10T5SW-24LED35DMVWHFR40SS	22.5"L x 3.0"W x 3.0"H / 35W 3,400L / White Finish / Frosted Lens / 4000K
10T5SW-48LED40DMVWHFR40SS	46.25"L x 3.0"W x 3.0"H / 40W 4,320L / White Finish / Frosted Lens / 4000K
10T5SW-48LED72DMVWHFR40SS	46.25"L x 3.0"W x 3.0"H / 72W 7,000L / White Finish / Frosted Lens / 4000K
10T5SW-96LED80DMVWHFR40SS	94.43"L x 3.0"W x 3.0"H / 80W 8,000L / White Finish / Frosted Lens / 4000K
10T5SW-96LED114DMVWHFR40SS	94.43"L x 3.0"W x 3.0"H / 114W 10,250L / White Finish / Frosted Lens / 4000K

Also available in 30K, 35K, & 50K.

## Lensed Strip With Integral Microwave Sensor

An integral microwave sensor features adjustable time, reach, and dusk-to-dawn sensitivity, and is factory installed discretely behind the lens.

ITEM NO.	DESCRIPTION
44FSF-48LED30DMVFR40SSM	48.0"L x 4.25"W x 3.25"H / 30W 3,300L / Frosted Lens / 4000K
44FSF-96LED57DMVFR40SSM	96.0"L x 4.25"W x 3.25"H / 57W 6,270L / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K. NOTE: Sensor may cause some shadowing.

## Contoured Strip With Sensor


Whether it's wall, ceiling, surface, or pendant mounted, this fixture can be used individually or joined together for continuous runs. It features a frosted diffuser that surrounds the LEDs for soft lighting.

ITEM NO.	DESCRIPTION
LDA-24LED15DMVWHFR40SS	23.6"L x 3.79"W x 3.93"H / 15W 1,500L / White Finish / Ribbed Frosted Lens / 4000K
LDA-24LED20DMVWHFR40SS	23.6"L x 3.79"W x 3.93"H / 20W 2,000L / White Finish / Ribbed Frosted Lens / 4000K
LDA-48LED30DMVWHFR40SS	47.2"L x 3.79"W x 3.93"H / 30W 3,000L / White Finish / Ribbed Frosted Lens / 4000K
LDA-48LED40DMVWHFR40SS	47.2"L x 3.79"W x 3.93"H / 40W 4,000L / White Finish / Ribbed Frosted Lens / 4000K
LDA-96LED60DMVWHFR40SS	94.4"L x 3.79"W x 3.93"H / 60W 6,000L / White Finish / Ribbed Frosted Lens / 4000K
LDA-96LED80DMVWHFR40SS	94.4"L x 3.79"W x 3.93"H / 80W 8,000L / White Finish / Ribbed Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

# STRIPS

## 1 Style, 3 Configurations!



### Enclosed With Hinged Frosted Lens



ITEM NO.	DESCRIPTION
MRRS-48LED28DMVWHFR40	48.0"L x 2.9"W x 3.4"H / 28W 2,700L / White Finish / Frosted Lens / 4000K
MRRS-48LED48DMVWHFR40	48.0"L x 2.9"W x 3.4"H / 48W 4,600L / White Finish / Frosted Lens / 4000K
MRRS-48LED57DMVWHFR40	48.0"L x 2.9"W x 3.4"H / 57W 5,400L / White Finish / Frosted Lens / 4000K
MRRS-96LED57DMVWHFR40	96.0"L x 2.9"W x 3.4"H / 57W 5,400L / White Finish / Frosted Lens / 4000K
MRRS-96LED96DMVWHFR40	96.0"L x 2.9"W x 3.4"H / 96W 9,200L / White Finish / Frosted Lens / 4000K
MRRS-96LED114DMVWHFR40	96.0"L x 2.9"W x 3.4"H / 114W 10,800L / White Finish / Frosted Lens / 4000K

Also available in 30K, 35K, & 50K.

### Deep Enhanced White Reflector



ITEM NO.	DESCRIPTION
MRRS-48LED28DMVWH40XWN	48.0"L x 2.9"W x 6.2"H / 28W 2,700L / White Finish / White Narrow Reflector / 4000K
MRRS-48LED48DMVWH40XWN	48.0"L x 2.9"W x 6.2"H / 48W 4,600L / White Finish / White Narrow Reflector / 4000K
MRRS-48LED57DMVWH40XWN	48.0"L x 2.9"W x 6.2"H / 57W 5,400L / White Finish / White Narrow Reflector / 4000K
MRRS-96LED57DMVWH40XWN	96.0"L x 2.9"W x 6.2"H / 57W 5,400L / White Finish / White Narrow Reflector / 4000K
MRRS-96LED96DMVWH40XWN	96.0"L x 2.9"W x 6.2"H / 96W 9,200L / White Finish / White Narrow Reflector / 4000K
MRRS-96LED114DMVWH40XWN	96.0"L x 2.9"W x 6.2"H / 114W 10,800L / White Finish / White Narrow Reflector / 4000K

Also available in 30K, 35K, & 50K.

### Open Strip



ITEM NO.	DESCRIPTION
MRRS-48LED28DMVWH40	48.0"L x 2.9"W x 1.8"H / 28W 2,700L / White Finish / 4000K
MRRS-48LED48DMVWH40	48.0"L x 2.9"W x 1.8"H / 48W 4,600L / White Finish / 4000K
MRRS-48LED57DMVWH40	48.0"L x 2.9"W x 1.8"H / 57W 5,400L / White Finish / 4000K
MRRS-96LED57DMVWH40	96.0"L x 2.9"W x 1.8"H / 57W 5,400L / White Finish / 4000K
MRRS-96LED96DMVWH40	96.0"L x 2.9"W x 1.8"H / 96W 9,200L / White Finish / 4000K
MRRS-96LED114DMVWH40	96.0"L x 2.9"W x 1.8"H / 114W 10,800L / White Finish / 4000K

Also available in 30K, 35K, & 50K.

### Industrial LED (Ideal For Ceilings Between 10 And 18 Feet)

Great for factories, warehouses, workshops, garages, and utility areas where concentrated light output is required.



For continuous run applications and wiring harnesses for electrical plug and play, see page 26.

ITEM NO.	DESCRIPTION
1-48LED30DMV40	48.0"L x 10.25"W x 4.25"H / 30W 4,310L / 4000K
1-48LED48DMV40	48.0"L x 10.25"W x 4.25"H / 48W 6,475L / 4000K
1-48LED57DMV40	48.0"L x 10.25"W x 4.25"H / 57W 7,755L / 4000K
1-96LED57DMV40	96.0"L x 10.25"W x 4.25"H / 57W 7,755L / 4000K
1-96LED97DMV40	96.0"L x 10.25"W x 4.25"H / 97W 12,950L / 4000K
1-96LED118DMV40	96.0"L x 10.25"W x 4.25"H / 118W 15,510L / 4000K

Add "EM" for emergency. To add wire guard, order A71 separately (order 2 for 96"). Also available in 30K, 35K, & 50K.



# STRIPS



## Economy Lensed Strip (Ideal For Cove Lights)

ITEM NO.	DESCRIPTION
42E-24LED20DMVWHFR40	24"L x 2"W x 3"H / 20W 2,160L / White Finish / Frosted Lens / 4000K
42E-48LED28DMVWHFR40	46"L / 2"W x 3"H / 28W 2,700L / White Finish / Frosted Lens / 4000K
42E-48LED48DMVWHFR40	46"L / 2"W x 3"H / 48W 4,100L / White Finish / Frosted Lens / 4000K
42E-96LED57DMVWHFR40	92"L / 2"W / 3"H / 57W 5,400L / White Finish / Frosted Lens / 4000K
42E-96LED72DMVWHFR40	92"L / 2"W / 3"H / 72W 7,000L / White Finish / Frosted Lens / 4000K
42E-96LED96DMVWHFR40	92"L / 2"W / 3"H / 96W 10,200L / White Finish / Frosted Lens / 4000K

For continuous runs, add "PI1" or "PI3D" after color temperature for through wiring harness. Also available in 30K, 35K, & 50K.



For continuous run applications and wiring harnesses for electrical plug and play, see page 26.

## Economy Round Lensed Strip (Ideal For Continuous Runs)

ITEM NO.	DESCRIPTION
44FSF-48LED30DMVFR40	48.0"L x 4.25"W x 3.25"H / 30W 3,300L / Round Frosted Lens / 4000K
44FSF-48LED57DMVFR40	48.0"L x 4.25"W x 3.25"H / 57W 6,270L / Round Frosted Lens / 4000K
44FSF-96LED57DMVFR40	96.0"L x 4.25"W x 3.25"H / 57W 6,270L / Round Frosted Lens / 4000K
44FSF-96LED118DMVFR40	96.0"L x 4.25"W x 3.25"H / 118W 12,980L / Round Frosted Lens / 4000K

Also available in 30K, 35K, & 50K.



## LED Premium Lensed Strip (Ideal For Continuous Runs)

Create different looks with a round or flat lens. Excellent for schools, retail stores, warehouses, and storage facilities.

ITEM NO.	DESCRIPTION
44RSR-48LED30DMV40	48.50"L x 4.36"W x 3.90"H / 30W 3,827L / Round Lens / 4000K
44RSR-48LED58DMV40	48.50"L x 4.36"W x 3.90"H / 58W 7,013L / Round Lens / 4000K
44RSR-96LED60DMV40	96.0"L x 4.36"W x 3.90"H / 60W 7,654L / Round Lens / 4000K
44RSR-96LED116DMV40	96.0"L x 4.36"W x 3.90"H / 116W 14,026L / Round Lens / 4000K
44RSF-48LED30DMV40	48.50"L x 4.36"W x 2.78"H / 30W 3,529L / Flat Lens / 4000K
44RSF-48LED58DMV40	48.50"L x 4.36"W x 2.78"H / 58W 6,717L / Flat Lens / 4000K
44RSF-96LED60DMV40	96.0"L x 4.36"W x 2.78"H / 60W 6,952L / Flat Lens / 4000K
44RSF-96LED116DMV40	96.0"L x 4.36"W x 2.78"H / 116W 13,434L / Flat Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## New Product!



## Medium Body Round Lensed Strip With Reflector

This fixture is ideal for warehouse, retail, and utility areas requiring general illumination in a commercial quality strip configuration.

ITEM NO.	DESCRIPTION
1FSF-24LED24DMV40W30	24.05"L x 8.06"W x 2.0"H / 24W 3,450L / Frosted Lens / 4000K / Symmetrical Reflector
1FSF-24LED1U3D30DMV40W30	24.05"L x 8.06"W x 2.0"H / 30W 1,075L Up 3,225L Down / Frosted Lens / 4000K / Symmetrical Reflector
1FSF-48LED48DMV40W30	48.0"L x 8.06"W x 2.0"H / 48W 6,900L / Frosted Lens / 4000K / Symmetrical Reflector
1FSF-48LED1U3D60DMV40W30	48.0"L x 8.06"W x 2.0"H / 60W 2,150L Up 6,450L Down / Frosted Lens / 4000K / Symmetrical Reflector
1FSF-96LED96DMV40W30	96.0"L x 8.06"W x 2.0"H / 96W 12,400L / Frosted Lens / 4000K / Symmetrical Reflector
1FSF-96LED1U3D120DMV40W30	96.0"L x 8.06"W x 2.0"H / 120W 3,875L Up 11,625L Down / Frosted Lens / 4000K / Symmetrical Reflector

Add "EM" for emergency. Change "W30" to "W35" for asymmetrical reflector. Also available in 30K, 35K, & 50K.

# STRIPS

## Linear Round Surface (Ideal For Vanity Lighting)

ITEM NO.	DESCRIPTION
10T5-24LED18DMVWHSW40	22.5"L x 2.2"W x 2.6"H / 18W 1,700L / White Finish / Smooth White Lens / 4000K
10T5-48LED35DMVWHSW40	46.25"L x 2.2"W x 2.6"H / 35W 3,240L / White Finish / Smooth White Lens / 4000K
10T5W-48LED40DMVWHSW40	46.25"L x 3.0"W x 3.0"H / Wide Body / 40W 4,000L / White Finish / Smooth White Lens / 4000K
10T5W-96LED80DMVWHSW40	92.0"L x 3.0"W x 3.0"H / Wide Body / 80W 8,000L / White Finish / Smooth White Lens / 4000K

Add "EM" for emergency (only for wide body). Also available in 30K, 35K, & 50K. Consult for other finish options.

## Linear Square Surface Strip

Square lensed version of above fixture.

ITEM NO.	DESCRIPTION
10T5S-24LED12DMVWHFR40	22.5"L x 2.0"W x 2.6"H / 12W 1,080L / White Finish / Frosted Lens / 4000K
10T5S-48LED28DMVWHFR40	46.25"L x 2.0"W x 2.6"H / 28W 2,520L / White Finish / Frosted Lens / 4000K
10T5S-48LED40DMVWHFR40	46.25"L x 2.0"W x 2.6"H / 35W 3,240L / White Finish / Frosted Lens / 4000K
10T5S-96LED57DMVWHFR40	92.0"L x 2.0"W x 2.6"H / 57W 5,400L / White Finish / Frosted Lens / 4000K
10T5S-96LED72DMVWHFR40	92.0"L x 2.0"W x 2.6"H / 72W 6,480L / White Finish / Frosted Lens / 4000K

Only available with remote EM. Also available in 30K, 35K, & 50K. Consult for other finish options.

## Wide Body Surface Linear Strip

A slightly wider version of the above square lensed strip allows for higher output in shorter runs and an integral emergency driver.

ITEM NO.	DESCRIPTION
10T5SW-24LED35DMVWHFR40	22.5"L x 3.0"W x 3.0"H / Wide Body / 35W 3,400L / White Finish / Frosted Lens / 4000K
10T5SW-48LED40DMVWHFR40	46.25"L x 3.0"W x 3.0"H / Wide Body / 40W 4,000L / White Finish / Frosted Lens / 4000K
10T5SW-48LED72DMVWHFR40	46.25"L x 3.0"W x 3.0"H / Wide Body / 72W 7,000L / White Finish / Frosted Lens / 4000K
10T5SW-96LED80DMVWHFR40	92"L x 3"W x 3"H / Wide Body / 80W 8,000L / White Finish / Frosted Lens / 4000K
10T5SW-96LED114DMVWHFR40	92"L x 3"W x 3"H / Wide Body / 114W 10,250L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Remove "S" for round lensed version. Also available in 30K, 35K, & 50K. Consult for other finish options. For sensor, add "SS" after the color temperature.

## LED Surface Lensed Strip (4.25" Wide)


Low profile economy linear strip provides light right where you need it.

ITEM NO.	DESCRIPTION
44-24LED24DMVFR40	24.0"L x 4.25"W x 2.95"H / 24W 2,980L / Frosted Lens / 4000K
44-24LED30DMVFR40	24.0"L x 4.25"W x 2.95"H / 30W 3,433L / Frosted Lens / 4000K
44-48LED35DMVFR40	48.0"L x 4.25"W x 2.95"H / 35W 4,525L / Frosted Lens / 4000K
44-48LED48DMVFR40	48.0"L x 4.25"W x 2.95"H / 48W 5,955L / Frosted Lens / 4000K
44-48LED57DMVFR40	48.0"L x 4.25"W x 2.95"H / 57W 7,120L / Frosted Lens / 4000K
44-96LED70DMVFR40	96.0"L x 4.25"W x 2.95"H / 70W 9,050L / Frosted Lens / 4000K
44-96LED97DMVFR40	96.0"L x 4.25"W x 2.95"H / 97W 11,910L / Frosted Lens / 4000K
44-96LED118DMVFR40	96.0"L x 4.25"W x 2.95"H / 118W 14,235L / Frosted Lens / 4000K

For wire guard, order as "A69". Add "EM" for emergency. Also available in 30K, 35K, & 50K.



Vented body for emergency option.



Optional wire guard A69.

# STRIPS

## LED Open Strip (4.25" Wide) Consult To Add Reflectors

This strip is ideal for warehouses, utility areas, and retail spaces requiring general illumination with a commercial wide strip configuration.

ITEM NO.	DESCRIPTION
44-24LED24DMV40	24.0"L x 4.25"W x 2.95"H / 24W 3,355L / 4000K
44-24LED30DMV40	24.0"L x 4.25"W x 2.95"H / 30W 3,925L / 4000K
44-48LED35DMV40	48.0"L x 4.25"W x 2.95"H / 35W 4,920L / 4000K
44-48LED48DMV40	48.0"L x 4.25"W x 2.95"H / 48W 6,475L / 4000K
44-48LED57DMV40	48.0"L x 4.25"W x 2.95"H / 57W 7,755L / 4000K
44-96LED70DMV40	96.0"L x 4.25"W x 2.95"H / 70W 9,840L / 4000K
44-96LED97DMV40	96.0"L x 4.25"W x 2.95"H / 97W 12,950L / 4000K
44-96LED118DMV40	96.0"L x 4.25"W x 2.95"H / 118W 15,510L / 4000K

For wire guard, order "A69" (see page 18). Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## LED Open Strip (2.75" Wide)

This fixture is a narrow version of our standard strip.

ITEM NO.	DESCRIPTION
42-24LED18DMV40	24.0"L x 2.75"W x 1.8"H / 18W 2,590L / 4000K
42-48LED24DMV40	48.0"L x 2.75"W x 1.8"H / 24W 3,475L / 4000K
42-48LED30DMV40	48.0"L x 2.75"W x 1.8"H / 30W 4,310L / 4000K
42-48LED35DMV40	48.0"L x 2.75"W x 1.8"H / 35W 4,920L / 4000K
42-96LED57DMV40	96.0"L x 2.75"W x 1.8"H / 57W 7,755L / 4000K
42-96LED70DMV40	96.0"L x 2.75"W x 1.8"H / 70W 9,840L / 4000K

Add "EM" for emergency. Add "FR" after "DMV" for lensed version. Also available in 30K, 35K, & 50K.

## Trapezoidal Lensed Channel

This series is the right choice for merchandising products or general lighting applications.

ITEM NO.	DESCRIPTION
42T-48LED30DMVWHFR40	48.0"L x 3.5"W x 2.7"H / 30W 3,150L / White Finish / Frosted Lens / 4000K
42T-48LED38DMVWHFR40	48.0"L x 3.5"W x 2.7"H / 38W 3,990L / White Finish / Frosted Lens / 4000K
42T-48LED57DMVWHFR40	48.0"L x 3.5"W x 2.7"H / 45W 4,700L / White Finish / Frosted Lens / 4000K
42T-96LED57DMVWHFR40	96.0"L x 3.5"W x 2.7"H / 60W 6,300L / White Finish / Frosted Lens / 4000K
42T-96LED60DMVWHFR40	96.0"L x 3.5"W x 2.7"H / 75W 7,900L / White Finish / Frosted Lens / 4000K
42T-96LED90DMVWHFR40	96.0"L x 3.5"W x 2.7"H / 90W 9,450L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## 1.63" Wide Open Strip

This fixture is micro version of our standard strip.

ITEM NO.	DESCRIPTION
41-48LED24DMV40	48.0"L x 1.63"W x 1.38"H / 24W 2,800L / 4000K
41-48LED28DMV40	48.0"L x 1.63"W x 1.38"H / 28W 3,200L / 4000K
41-48LED35DMV40	48.0"L x 1.63"W x 1.38"H / 35W 4,800L / 4000K
41-96LED48DMV40	96.0"L x 1.63"W x 1.38"H / 48W 5,600L / 4000K
41-96LED57DMV40	96.0"L x 1.63"W x 1.38"H / 57W 6,400L / 4000K
41-96LED67DMV40	96.0"L x 1.63"W x 1.38"H / 67W 7,500L / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Linear Strip (Ideal Replacement For Fluorescent Strips)


ITEM NO.	DESCRIPTION
LSBR-48LED35DMV40	48.0"L x 2.88"W x 3.76"H / 35W 4,650L / 4000K
LSBR-96LED46DMV40	95.94"L x 2.88"W x 3.76"H / 46W 6,050L / 4000K
LSBR-96LED65DMV40	95.94"L x 2.88"W x 3.76"H / 65W 8,700L / 4000K

Add "EM" for emergency. Also available in 50K.



# Linear Pendant

Modern Lighting offers a wide range of linear pendant fixtures featuring the most cutting-edge technology and contemporary styles. Linear configurations provide a sleek, modern aesthetic for high-end commercial offices, retail establishments, and educational facilities. Our steel fixtures are fabricated in our USA facility to provide individual customization and faster lead times.



For continuous runs, see page 26.

Consult for other finish options!

## Linear 2" x 3" Pendant (Uplight Or Downlight Only)

Our signature 2" wide pendant is fitting for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

ITEM NO.	DESCRIPTION
L23-P48LED26DMVWHSF40H6W5	48"L x 2"W x 3"H / 26W 2,600L / White Finish / Frosted Lens / 4000K
L23-P48LED38DMVWHSF40H6W5	48"L x 2"W x 3"H / 38W 3,800L / White Finish / Frosted Lens / 4000K
L23-P48LED45DMVWHSF40H6W5	48"L x 2"W x 3"H / 45W 4,500L / White Finish / Frosted Lens / 4000K
L23-P96LED52DMVWHSF40H6W5	96"L x 2"W x 3"H / 52W 5,200L / White Finish / Frosted Lens / 4000K
L23-P96LED76DMVWHSF40H6W5	96"L x 2"W x 3"H / 76W 7,600L / White Finish / Frosted Lens / 4000K
L23-P96LED90DMVWHSF40H6W5	96"L x 2"W x 3"H / 90W 9,000L / White Finish / Frosted Lens / 4000K

Add "EM" for remote mounted emergency. Add "SS" for integral occupancy sensor (adds roughly 3" to fixture length). Remove "H6W5" for surface mount. Also available in 30K, 35K, & 50K.

## Linear 2" x 3" Pendant (Uplight And Downlight)

Our signature 2" wide pendant designed specifically for uplight and downlight.

ITEM NO.	DESCRIPTION
L23-P48LED1U2D36DMVWHSF40H6W5	48"L x 2"W x 3"H / 36W 600L Up 1,200L Down / White Finish / Frosted Lens / 4000K
L23-P48LED1U2D54DMVWHSF40H6W5	48"L x 2"W x 3"H / 54W 1,800L Up 3,600L Down / White Finish / Frosted Lens / 4000K
L23-P96LED1U2D72DMVWHSF40H6W5	96"L x 2"W x 3"H / 72W 2,400L Up 4,800L Down / White Finish / Frosted Lens / 4000K
L23-P96LED1U2D108DMVWHSF40H6W5	96"L x 2"W x 3"H / 108W 3,600L Up 7,200L Down / White Finish / Frosted Lens / 4000K

Add "EM" for remote mounted emergency. Add "SS" for integral occupancy sensor (adds roughly 3" to fixture length). Also available in 30K, 35K, & 50K.






# LINEAR PENDANT

Dress up your linear strip with “hot” colors that will attract attention in your space. We can powder coat any finish with an economical adder. Whether wall, ceiling, surface, or pendant mounted, vertical or horizontal orientation, this fixture does it all! The LDA-LED is available in 3 different sizes and can be used individually or in continuous runs. See page 26 for continuous run wiring harness.

**IDEAL FOR ALL APPLICATIONS!**



Orange (OR)



Red (RD)



Matte White (WH)



Black (BK)

## LED Contoured Strip

The frosted diffuser on the LDA is specifically designed to the LED module to surround the LEDs for soft lighting.

### ITEM NO.

### DESCRIPTION

ITEM NO.	DESCRIPTION
LDA-24LED15DMVWHRF40H4W5	23.60”L x 3.79”W x 3.93”H / 15W 1,500L / White Finish / Ribbed Frosted Lens / 4000K
LDA-24LED20DMVWHRF40H4W5	23.60”L x 3.79”W x 3.93”H / 20W 2,000L / White Finish / Ribbed Frosted Lens / 4000K
LDA-48LED30DMVWHRF40H4W5	47.20”L x 3.79”W x 3.93”H / 30W 3,000L / White Finish / Ribbed Frosted Lens / 4000K
LDA-48LED40DMVWHRF40H4W5	47.20”L x 3.79”W x 3.93”H / 40W 4,000L / White Finish / Ribbed Frosted Lens / 4000K
LDA-96LED60DMVWHRF40H4W5	94.40”L x 3.79”W x 3.93”H / 60W 6,000L / White Finish / Ribbed Frosted Lens / 4000K
LDA-96LED80DMVWHRF40H4W5	94.40”L x 3.79”W x 3.93”H / 80W 8,000L / White Finish / Ribbed Frosted Lens / 4000K



Also available in 30K, 35K, & 50K.

# LINEAR PENDANT

## Linear 2.5" x 3.5" Pendant

Our signature 2.5" wide pendant is perfect for corridors, offices, and lobbies.

### ITEM NO.

### DESCRIPTION

LD23-48LED28DMVWHFR40H4W5	48"L x 2.38"W x 3.25"H / 28W 2,800L / White Finish / Frosted Lens / 4000K
LD23-48LED40DMVWHFR40H4W5	48"L x 2.38"W x 3.25"H / 40W 4,000L / White Finish / Frosted Lens / 4000K
LD23-48LED45DMVWHFR40H4W5	48"L x 2.38"W x 3.25"H / 45W 4,500L / White Finish / Frosted Lens / 4000K
LD23-96LED56DMVWHFR40H4W5	96"L x 2.38"W x 3.25"H / 56W 5,600L / White Finish / Frosted Lens / 4000K
LD23-96LED62DMVWHFR40H4W5	96"L x 2.38"W x 3.25"H / 62W 6,200L / White Finish / Frosted Lens / 4000K
LD23-96LED80DMVWHFR40H4W5	96"L x 2.38"W x 3.25"H / 80W 8,000L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Remove "H4W5" for surface mount. Also available in 30K, 35K, & 50K.

## Linear 4" x 4" Pendant

Our signature 4" wide pendant is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

### ITEM NO.

### DESCRIPTION

L44-P48LED24DMVWHSF40H4W5	48"L x 4"W x 4"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L44-P48LED48DMVWHSF40H4W5	48"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-P96LED48DMVWHSF40H4W5	96"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-P96LED97DMVWHSF40H4W5	96"L x 4"W x 4"H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Remove "H4W5" for surface mount. Also available in 30K, 35K, & 50K.

## Linear 4" x 4" Sensor Ready Pendant


Our signature 4" wide pendant is ideal for corridors, offices, and lobbies and features an integrated occupancy sensor.

### ITEM NO.

### DESCRIPTION

L44-P48LED24DMVWHSF40SSH4W5	48"L x 4"W x 4"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L44-P48LED48DMVWHSF40SSH4W5	48"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-P96LED48DMVWHSF40SSH4W5	96"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-P96LED97DMVWHSF40SSH4W5	96"L x 4"W x 4"H / 97W 9,600L / White Finish / Frosted Lens / 4000K


"SS" comes standard with occupancy sensor. Change "SS" to "SSD" for daylight harvesting. Also available in 30K, 35K, & 50K.



Consult for other finish options.



For continuous runs, see page 26.





# LINEAR PENDANT

## 4" x 4" Indirect Linear Pendant

The unique structure of this fixture, with no horizontal lens or diffuser, stands out among other linear style pendants. Specially engineered LED arrays lay discretely on the bottom edge of the linear channel to brightly illuminate the barreled reflector and provide a soft downward spread of light.



### ITEM NO.

### DESCRIPTION

ITEM NO.	DESCRIPTION
L44IR-P24LED25DMVWH40H6W5	24.0"L x 4.02"W x 4.02"H / 25W 2,000L / White Finish / 4000K
L44IR-P48LED50DMVWH40H6W5	48.18"L x 4.02"W x 4.02"H / 50W 4,000L / White Finish / 4000K
L44IR-P96LED100DMVWH40H6W5	96.0"L x 4.02"W x 4.02"H / 100W 8,000L / White Finish / 4000K

Also available in 30K, 35K, & 50K. For continuous runs, see page 26.

## Architectural Trapezoidal Pendant

This slim, 2.8" wide fixture creates a unique architectural look, and provides your choice of blue, black, or white end caps.

### ITEM NO.

### DESCRIPTION

ITEM NO.	DESCRIPTION
ATP-48LED24DMVWHWHFR40	47.0"L x 2.8"W x 2.8"H / 24W 2,050L / White Finish / White End Caps / Frosted Lens / 4000K
ATP-48LED34DMVWHWHFR40	47.0"L x 2.8"W x 2.8"H / 34W 3,150L / White Finish / White End Caps / Frosted Lens / 4000K
ATP-48LED43DMVWHWHFR40	47.0"L x 2.8"W x 2.8"H / 43W 4,000L / White Finish / White End Caps / Frosted Lens / 4000K
ATP-48LED57DMVWHWHFR40	47.0"L x 2.8"W x 2.8"H / 57W 5,100L / White Finish / White End Caps / Frosted Lens / 4000K

Also available in 30K, 35K, & 50K. For continuous runs, see page 26.

## Linear 4" x 5" Pendant (Uplight & Downlight)



Designed specifically for uplight and downlight applications, this 4"x5" pendant is ideal for corridors, offices, and lobbies where direct/indirect lighting is needed.

### ITEM NO.

### DESCRIPTION

ITEM NO.	DESCRIPTION
L45-P48LED1U2D36DMVWHSF40H4W5	48.0"L x 4.0"W x 5.1"H / 36W 1,200L Up 2,400L Down / White Finish / Frosted Lens / 4000K
L45-P48LED1U2D54DMVWHSF40H4W5	48.0"L x 4.0"W x 5.1"H / 54W 1,800L Up 3,600L Down / White Finish / Frosted Lens / 4000K
L45-P48LED1U2D72DMVWHSF40H4W5	48.0"L x 4.0"W x 5.1"H / 72W 2,400L Up 4,800L Down / White Finish / Frosted Lens / 4000K
L45-P96LED1U2D72DMVWHSF40H4W5	96.0"L x 4.0"W x 5.1"H / 72W 2,400L Up 4,800L Down / White Finish / Frosted Lens / 4000K
L45-P96LED1U2D108DMVWHSF40H4W5	96.0"L x 4.0"W x 5.1"H / 108W 3,600L Up 7,200L Down / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K. For continuous runs, see page 26.



# LINEAR PENDANT



## Linear 6"x 6" Pendant (Uplight Or Downlight Only)

Our signature 6" wide pendant is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

ITEM NO.	DESCRIPTION
L66-P48LED24DMVWHSF40H4W5	47.94"L x 5.75"W x 6.0"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L66-P48LED48DMVWHSF40H4W5	47.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-P96LED48DMVWHSF40H4W5	95.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-P96LED97DMVWHSF40H4W5	95.94"L x 5.75"W x 6.0"H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Remove "H4W5" for surface mount. Change "SF" to "MW" for matte white lens. Also available in 30K, 35K, & 50K. For continuous runs, see page 26.

## Linear 6"x 6" Pendant (Uplight & Downlight)

Our signature 6" wide pendant designed specifically for uplight and downlight.

ITEM NO.	DESCRIPTION
L66-P48LED1U2D36DMVWHSF40H4W5	47.94"L x 5.75"W x 6.0"H / 36W 1,200L Up 2,400L Down / White Finish / Frosted Lens / 4000K
L66-P48LED1U2D72DMVWHSF40H4W5	47.94"L x 5.75"W x 6.0"H / 72W 2,400L Up 4,800L Down / White Finish / Frosted Lens / 4000K
L66-P96LED1U2D72DMVWHSF40H4W5	95.94"L x 5.75"W x 6.0"H / 72W 2,400L Up 4,800L Down / White Finish / Frosted Lens / 4000K
L66-P96LED1U2D108DMVWHSF40H4W5	95.94"L x 5.75"W x 6.0"H / 108W 3,600L Up 7,200L Down / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Change "SF" to "MW" for matte white lens. Also available in 30K, 35K, & 50K. For continuous runs, see page 26.



Louvered option available!

## Linear Hanging Kits

Series	Canopy Finish	# Of Wires	Cord Finish
<b>A-HC301</b> 4ft. Canopy Cable Kit w/ 1 Power Feed & 1 Non-Power Feed	<b>WH</b> White	<b>(Blank)</b> 3 Wires (White, Black, Green)	<b>(Blank)</b> White
<b>A-HC302</b> 12ft. Canopy Cable Kit w/ 1 Power Feed & 1 Non-Power Feed	<b>BK</b> Black	<b>4W</b> 4 Wires (White, Black, Green, Blue For Emergency)	<b>BK</b> Black
<b>A-HC401</b> 4ft. Canopy Cable Kit w/ 1 Power Feed & 1 Non-Power Feed	<b>SL</b> Silver	<b>5W</b> 5 Wires (White, Black, Green, Violet, Gray For Dimming)	<b>SL</b> Silver
<b>A-HC402</b> 12ft. Canopy Cable Kit w/ 1 Power Feed & 1 Non-Power Feed		<b>6W</b> 6 Wires (White, Black, Red, Green, Violet, Gray For Dimming)	



HC301/302



HC401/402



# LINEAR PENDANT CONFIGURATIONS



**IF YOU CAN  
DREAM IT, WE  
CAN MAKE IT!**

## 4" x 4" Square In 4Ft. Sq & 8Ft. Sq (Downlight, 6 or 8 Watts Per Foot)

Create dramatic geometric lines of light in 4ft. or 8ft. squares. These squares feature lit corners, shadowless LED, and energy-efficient performance to provide excellent general lighting.

### ITEM NO.

### DESCRIPTION

SQ44-4x4LED96DMVWHSF40H4W5	4"L x 4"W 4ft. Sq / 96W 9,600L / White Finish / Frosted Lens / 4000K
SQ44-4x4LED128DMVWHSF40H4W5	4"L x 4"W 4ft. Sq / 128W 12,800L / White Finish / Frosted Lens / 4000K
SQ44-8x8LED192DMVWHSF40H4W5	4"L x 4"W 8ft. Sq / 192W 19,200L / White Finish / Frosted Lens / 4000K
SQ44-8x8LED256DMVWHSF40H4W5	4"L x 4"W 8ft. Sq / 256W 25,600L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K. Consult for up & downlight option.



*Consult for different configurations.  
(squares, rectangles, up & downlight  
versions, or different shapes of lit patterns)*

## Linear 4" x 4" Pendant (Downlight Only, Unlit Corners)

Use connectors with unlit corners to create dramatic patterns in "L", "T", and "X" shapes for custom configurations.

### ITEM NO.

### DESCRIPTION

L44-P48LED24DMVWHSF40PI3DH4W5	48"L x 4"W x 4"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L44-P48LED48DMVWHSF40PI3DH4W5	48"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-P96LED48DMVWHSF40PI3DH4W5	96"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-P96LED97DMVWHSF40PI3DH4W5	96"L x 4"W x 4"H / 97W 9,600L / White Finish / Frosted Lens / 4000K
L44_JB-1WAYPWH	Straight Joiner
L44_JB-2WAYPWH	90 Degree Joiner
L44_JB-3WAYPWH	T Connector (3 Way)
L44_JB-4WAYPWH	X Connector (4 Way)
L44_JB-ENDPWH	End Of Run

Add "EM" for emergency. Remove "H4W5" for surface mount. Also available in 30K, 35K, & 50K.

PATTERNS W/ NON-LIT CORNERS - Choose straight run L44 series pendants, and then choose appropriate non lit corner accessory (consult for L45 series up & down option or other sizes)




**T Connector (3 Way)**



**X Connector (4 Way)**



# LINEAR PENDANT CONFIGURATIONS



## 4"x 4" Linear X Series

Utilize the popular 4"x4" profile, create dramatic "X" shaped effect.

ITEM NO.	DESCRIPTION
X44-P2x2LED48DMVVWHSF40H4W5	4"L x 4"W 2x2 Cross / 48W Total & 12W Per 2ft. Run 4,800L / White Finish / Frosted Lens / 4000K
X44-P4x4LED96DMVVWHSF40H4W5	4"L x 4"W 4x4 Cross / 96W Total & 24W Per 4ft. Run 9,600L / White Finish / Frosted Lens / 4000K

Also available in 30K, 35K, & 50K. Consult for different shapes, sizes, or finishes.



## Ordering Patterns

Modern can create patterns with L23, L44, L45, and L66 series. Patterns are available for recessed and pendant mounting versions with lit or unlit corners. See below for some of the possibilities, and consult the factory for custom part numbers and pricing.



## Continuous Run Ordering For L23, L44, L45, L66, LPLIA, & LLP

1. Determine the run length and whether the run will be dimmed or not.
2. Use the above 2, 4, or 8ft. runs from the series specified to add up the total run length. Use the largest individual fixtures to achieve run lengths (i.e. for a 20ft. run, use 2x8 foot individuals and 1x4 foot individual from above with the correct ordering information for your series). Watts and lumens for each section should be proportional for the size (i.e. if 4ft. is 48W then 8ft. should be 96W). Consult for other lengths.
3. Designate each length required in the run whether it will be at the **beginning "B", joiner "J", or end of the run "E"**.
4. For Plug and Play electrical wiring between individual fixtures in the run, add one of the below harnesses. The number of wires is based on whether the run will be dimmable, with emergency, or just on/off.

## Refer To Spec Sheet For Placement Of Wiring Harness Code In Part Number

ITEM NO.	DESCRIPTION
PI1	3 Wire Harness (Normally For Non-Dim Applications)
PI2	4 Wire Harness (Normally For Emergency Circuit)
PI3D	5 Wire Harness (Normally For 0-10V Dimming)
PI4D	6 Wire Harness (Normally For 0-10V Dimming And Emergency)

# LINEAR PENDANT

## All-In-One Linear Channels

Based on your feedback, our All-In-One LED linear channel is new and improved to provide the easiest channel in the industry to specify, order, and install. This integral driver channel in two different profiles provides the ideal solution for both individual fixtures (in 4ft. or 8ft.), and joining multiple channels for longer, continuous runs (in 4ft. or 8ft. multiples). This beautifully-finished, low-cost, aluminum channel is so easy to install that both the “do-it-yourselfer” and professional installers can install in minutes. A specially-designed integral wiring harness (ordered separately) makes joining two channels electronically simple and efficient. A unique, mechanical joiner bracket in conjunction with our special joiner tool allows for joining two or more channels together with no light leak and clean connection.

AIOCSB

AIOCSA

### Features:

- Aluminum Channel
- Integral Driver
- Snap Fit Lens
- Magnetic Light Leak Block
- Integral Wire Harness



## Quick To Ship!

### All-In-One Channel Pendant Mount Kit

#### ITEM NO.

#### DESCRIPTION

AIOCSA-P48LED31DMVSA30H6W5	4'L x 2.16"W x 2.75"H / 31W 3,100L / Satin Aluminum Finish / 3000K
AIOCSA-P96LED62DMVSA30H6W5	8'L x 2.16"W x 2.75"H / 62W 6,200L / Satin Aluminum Finish / 3000K
AIOCSA-P144LED93DMVSA30H6W5	12'L x 2.16"W x 2.75"H / 93W 9,300L / Satin Aluminum Finish / 3000K
AIOCSA-P192LED124DMVSA30H6W5	16'L x 2.16"W x 2.75"H / 124W 12,400L / Satin Aluminum Finish / 3000K
AIOCSB-P48LED45DMVSA30H6W5	4'L x 3.54"W x 3.38"H / 45W 5,000L / Satin Aluminum Finish / 3000K
AIOCSB-P96LED90DMVSA30H6W5	8'L x 3.54"W x 3.38"H / 90W 10,000L / Satin Aluminum Finish / 3000K
AIOCSB-P144LED135DMVSA30H6W5	12'L x 3.54"W x 3.38"H / 135W 13,500L / Satin Aluminum Finish / 3000K
AIOCSB-P192LED180DMVSA30H6W5	16'L x 3.54"W x 3.38"H / 180W 18,000L / Satin Aluminum Finish / 3000K

Change "SA" to "WH" for white finish. Change "H6W5" to "H12W5" for 12ft. cable kit. Also available in 4000K.

*Kit includes: fixture, joining kits, cable kit, power feed, and non-power feed*

### All-In-One Channel Surface Mount Kit

#### ITEM NO.

#### DESCRIPTION



AIOCSA-S48LED31DMVSA30	4'L x 2.16"W x 2.75"H / 31W 3,100L / Satin Aluminum Finish / 3000K
AIOCSA-S96LED62DMVSA30	8'L x 2.16"W x 2.75"H / 62W 6,200L / Satin Aluminum Finish / 3000K
AIOCSA-S144LED93DMVSA30	12'L x 2.16"W x 2.75"H / 93W 9,300L / Satin Aluminum Finish / 3000K
AIOCSA-S192LED124DMVSA30	16'L x 2.16"W x 2.75"H / 124W 12,400L / Satin Aluminum Finish / 3000K
AIOCSB-S48LED45DMVSA30	4'L x 3.54"W x 3.38"H / 45W 5,000L / Satin Aluminum Finish / 3000K
AIOCSB-S96LED90DMVSA30	8'L x 3.54"W x 3.38"H / 90W 10,000L / Satin Aluminum Finish / 3000K
AIOCSB-S144LED135DMVSA30	12'L x 3.54"W x 3.38"H / 135W 13,500L / Satin Aluminum Finish / 3000K
AIOCSB-S192LED180DMVSA30	16'L x 3.54"W x 3.38"H / 180W 18,000L / Satin Aluminum Finish / 3000K

Change "SA" to "WH" for white finish. Change "H6W5" to "H12W5" for 12ft. cable kit. Also available in 4000K.

*Kit includes: fixture and surface mount kit*



# LINEAR PENDANT



**Kit includes:** fixture, joining kits, cable kit, power feed, and non-power feed



2 LED strips provide 40% uplight

## Individual All-In-One Channels (Mounting Kits Sold Separately)

ITEM NO.	DESCRIPTION
AIOCSA-48LED31DMVSA40	48.0"L x 2.16"W x 2.75"H / 31W 3,100L / Satin Aluminum Finish / 4000K
AIOCSA-96LED62DMVSA40	96.0"L x 2.16"W x 2.75"H / 62W 6,200L / Satin Aluminum Finish / 4000K
AIOCSB-48LED45DMVSA40	48.0"L x 3.54"W x 3.38"H / 45W 5,000L / Satin Aluminum Finish / 4000K
AIOCSB-96LED90DMVSA40	96.0"L x 3.54"W x 3.38"H / 90W 10,000L / Satin Aluminum Finish / 4000K

Consult for other finish options. Also available in 30K.

## Two Mounting Options (Surface Or Pendant)

ITEM NO.	DESCRIPTION
AIOCSURF	Surface Mount Screw And Toggle Set Of 3 (Includes 24" Power Cord)
A-HCPF606WH5W	Pendant Mounting Power Feed Canopy Kit / 5 Wire For Up To 6ft. Drop
A-HCPF612WH5W	Pendant Mounting Power Feed Canopy Kit / 5 Wire For Up To 12ft. Drop
A-HCNPF606WH	Pendant Mounting Non-Power Feed Canopy Kit / 6ft. Cable With Canopy
A-HCNPF612WH	Pendant Mounting Non-Power Feed Canopy Kit / 12ft. Cable With Canopy

## Join Two Or More Channels Together

ITEM NO.	DESCRIPTION
AIOCJOINER-SA	Mechanical Joiner To Join 2 AIOCSA Channels
AIOCJOINER-SB	Mechanical Joiner To Join 2 AIOCSB Channels
AIOCJOINERTOOL	Tool Required To Use Mechanical Joiner (1 Per Installation Needed)
AIOCLENSTOOL	Tool Required To Remove Lens (1 Per Installation Needed)
AIOC5WMFH	Wiring Harness 5" To Join 2 Channels

## All-In-One Direct/Indirect Channel

Aluminum 2.2" profile with the perfect ratio of direct/indirect light.

ITEM NO.	DESCRIPTION
AIOCBF-48LED2U3D45DMVSA30H6W5	4'L x 2.17"W x 3.15"H / 18W 1,800L Up 27W 2,700L Down / Satin Aluminum Finish / 3000K
AIOCBF-96LED2U3D90DMVSA30H6W5	8'L x 2.17"W x 3.15"H / 36W 3,600L Up 54W 5,400L Down / Satin Aluminum Finish / 3000K
AIOCBF-144LED2U3D135DMVSA30H6W5	12'L x 2.17"W x 3.15"H / 54W 5,400L Up 81W 8,100L Down / Satin Aluminum Finish / 3000K
AIOCBF-192LED2U3D180DMVSA30H6W5	16'L x 2.17"W x 3.15"H / 72W 7,200L Up 108W 10,800L Down / Satin Aluminum Finish / 3000K

Consult for other finish options. Also available in 40K.


## AIOCBF Accessories

ITEM NO.	DESCRIPTION
<b>Drivers</b>	
A-HCPF705WWH	Pendant Mounting Kit Power Feed White Canopy 5 Wire Clear Cord & 6ft. Cable
A-HCPF7125WWH	Pendant Mounting Kit Power Feed White Canopy 5 Wire Clear Cord & 12ft. Cable
A-HCNPF705WWH	Pendant Mounting Kit Non-Power Feed White Canopy & 6ft. Cable
A-HCNPF712WWH	Pendant Mounting Kit Non-Power Feed White Canopy & 12ft. Cable
AIOCLENSTOOL	Tool Required To Remove Lens (1 Per Installation Needed)
AIOCJOINERTOOL	Tool Required To Use Mechanical Joiner (1 Per Installation Needed)

**New Product!**




# LINEAR PENDANT



## All-In-One Channel Rectangle

ITEM NO.	DESCRIPTION
AIOCSR-A4X8LED210DMVSA40H6W5	4' x 8' Rectangle With 2.16"W Channels / 210W 21,000L / Satin Aluminum Finish / 4000K
AIOCSR-A4X8LED210DMVWH40H6W5	4' x 8' Rectangle With 2.16"W Channels / 210W 21,000L / White Finish / 4000K



**New Product!**

*Make a bold statement with this geometric line of light! This 4x8, 2.2" linear rectangle is perfect for filling large spaces without impairing visibility.*



## All-In-One Channel Individual Fixture (Wet Location)



Now bring your exterior applications to life with a specially-designed wet location linear pendant. This aluminum extrusion is 3.5" wide for a bold yet minimal look with a sealed lens to keep out moisture and bugs.

ITEM NO.	DESCRIPTION
AIOCSW-48LED45DMVSA40H6W5	48.7"L x 3.58"W x 3.58"H / 45W 4,900L / Satin Aluminum Finish / 4000K
AIOCSW-96LED90DMVSA40H6W5	96.7"L x 3.58"W x 3.58"H / 90W 10,000L / Satin Aluminum Finish / 4000K


Includes 6ft. 5 wire dimming power feed with fast connector (one side) and fix clips for surface mount and pendant bracket (2 pieces per set). Also available in 50K.

**New Product!**

## AIOCSW Kits

ITEM NO.	DESCRIPTION
AIOCSW-48LED45DMVSA40H6W5-B	48.7"L x 3.58"W x 3.58"H / 45W 4,900L / Satin Aluminum Finish / Beginner
AIOCSW-48LED45DMVSA40H6W5-J	48.7"L x 3.58"W x 3.58"H / 45W 4,900L / Satin Aluminum Finish / Joiner
AIOCSW-48LED45DMVSA40H6W5-E	48.7"L x 3.58"W x 3.58"H / 45W 4,900L / Satin Aluminum Finish / End Run

Joiner and end run kits include: fixture, 8.67" black dimming wiring harness with fast connector (both sides), fix clips for surface mount and pendant bracket (2 pieces), and 180° straight connector (2 pieces per set). Beginner run kits include: fixture, 6ft. 5 wire dimming power feed with fast connector (one side) and fix clips for surface mount and pendant bracket (2 pieces per set). Replace "48" with "96" for 96" length.



*Mounting brackets and joiner accessories included*



# LINEAR CHANNELS WITH REMOTE DRIVERS

## Linear Square Pendant (1.75" Wide & 6 Watts Per Foot)



ITEM NO.	DESCRIPTION
LLCSH-48LED24SA30	47.24"L x 1.57"W x 2.54"H / 24W 2,125L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation
LLCSH-48LED24SA40	47.24"L x 1.57"W x 2.54"H / 24W 2,125L / Satin Aluminum Finish / 4000K / 10' Clear Wire For Installation
LLCSH-96LED49SA30	96.46"L x 1.57"W x 2.54"H / 49W 4,335L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation
LLCSH-96LED49SA40	96.46"L x 1.57"W x 2.54"H / 49W 4,335L / Satin Aluminum Finish / 4000K / 10' Clear Wire For Installation

See page 31 for remote driver options.

*Available in custom lengths and patterns. We make it easy!*

## LLCSH Pattern Options



ITEM NO.	DESCRIPTION
LLCSHCAP	End Cap
LLCSHLOCKER	Internal Locker For Gear Tray
LLCSHRECLIP	Recessed Screw Clip
LLCSHWALLCLIP	Wall Mount "L" Clip
LLCSHJOINER	Joiner Spline For LLCSH Extrusion
LLCSHJOINER30	90° Flat Corner 3000K
LLCSHJOINER40	90° Flat Corner 4000K
LLCSHTEE30	Flat "T" 3000K
LLCSHTEE40	Flat "T" 4000K
LLCSHCROSS30	Flat X-CROSS 3000K
LLCSHCROSS40	Flat X-CROSS 4000K
LLCSHHC601WH	LLCSH Pendant Parts Kit 6ft.
LLCSHHC602WH	LLCSH Pendant Parts Kit 12ft.

## LLCRA



ITEM NO.	DESCRIPTION
LLCRA-48LED35SA30	47.75"L x 1.6"Dia / 35W 2,246L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation
LLCRA-97LED69SA30	97.0"L x 1.6"Dia / 69W 4,492L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation


See next page for remote driver options. Hanging kit and remote driver sold separately. Also available in 40K.

## LLCRB

ITEM NO.	DESCRIPTION
LLCRB-47LED42SA30	47.75"L x 2.36"Dia / 42W 2,488L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation
LLCRB-96LED83SA30	96.0"L x 2.36"Dia / 83W 4,976L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation

See next page for remote driver options. Hanging kit and remote driver sold separately. Also available in 40K.

# LINEAR CHANNELS WITH REMOTE DRIVERS



## LLCSA

ITEM NO.	DESCRIPTION
LLCSA-48LED23SA30	47.75"L x 0.78"W x 0.77"H / 23W 1,500L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation
LLCSA-96LED46SA30	97.0"L x 0.78"W x 0.77"H / 46W 3,000L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation

See next page for remote driver options. Hanging kit and remote driver sold separately. Also available in 40K.

## LLCSB

ITEM NO.	DESCRIPTION
LLCSB-47LED42SA30	47.75"L x 1.38"W x 1.38"H / 42W 2,468L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation
LLCSB-96LED83SA30	96.0"L x 1.38"W x 1.38"H / 83W 4,976L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation

See below for remote driver options. Hanging kit and remote driver sold separately. Also available in 40K.

## LLCSC

ITEM NO.	DESCRIPTION
LLCSC-48LED58SA30	47.75"L x 1.92"W x 2.75"H / 58W 3,456L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation
LLCSC-97LED115SA30	97.0"L x 1.92"W x 2.75"H / 115W 6,912L / Satin Aluminum Finish / 3000K / 10' Clear Wire For Installation

See below for remote driver options. Hanging kit and remote driver sold separately. Also available in 40K.

## Drivers & Accessories (Choice Of Magnetic Or Electronic Drivers)

Magnetic drivers from Magnitude are dimmable with any standard MLV Triac dimmer or electronic driver. Drivers from AC Electronics are dimmable with 0-10V dimming. See driver specification sheets for details.



ITEM NO.	DESCRIPTION
<b>Drivers</b>	
LEDD-MDCV24V20-120VHW	Driver LED CV 20W MLV DIM 24V 120V HW
LEDD-MDCV24V40-120VHW	Driver LED CV 40W MLV DIM 24V 120V HW
LEDD-MDCV24V50-120VHW	Driver LED CV 50W MLV DIM 24V 120V HW
LEDD-MDCV24V60-120VHW	Driver LED CV 60W MLV DIM 24V 120V HW
LEDD-MDCV24V96-120VHW	Driver LED CV 96W MLV DIM 24V 120V HW
LEDD-MDCV24V150-120VHW	Driver LED CV 150W MLV DIM 24V 120V HW
LEDD-MDCV24V2VX96-120VHW	Driver LED CV 2x96W MLV DIM 24V 120V HW
LEDD-MDCV24V3VX96-120VHW	Driver LED CV 3x96W MLV DIM 24V 120V HW
LEDD-DCV24V30-MVHW	Driver LED CV 30W 0-10V DIM 24V 120-277V HW
LEDD-DCV24V60-MVHW	Driver LED CV 60W 0-10V DIM 24V 120-277V HW
LEDD-DCV24V96-MVHW	Driver LED CV 96W 0-10V DIM 24V 120-277V HW
<b>Cable Kits</b>	
HC601WH	Cable Kit With 6' Cable & Power Feed/Cable & White Canopy Included
HC602WH	Cable Kit With 12' Cable & Power Feed/Cable & White Canopy Included
<b>Joiners</b>	
LLCRAJOIN	Mechanical Joiner Spline For LLCRA & LLCSC
LLCSAJOIN	Mechanical Joiner Spline For LLCRB, LLCSA, & LLCSCB



# LINEAR PENDANTS

## LPLIA With Direct/Indirect Lighting

When suspended, this sleek, compact, low profile ellipse appears to float in a space, and is specially designed for direct/indirect lighting.



### ITEM NO.

### DESCRIPTION

LPLIA-48LED1U2D36DMVWH40H4W5	47.0"L x 10.8"W x 3.94"H / 36W 1,595L Up 3,190L Down / White Finish / Frosted Downlight Lens No Uplight Lens / 4000K
LPLIA-48LED1U2D60DMVWH40H4W5	47.0"L x 10.8"W x 3.94"H / 60W 2,630L Up 5,260L Down / White Finish / Frosted Downlight Lens No Uplight Lens / 4000K
LPLIA-96LED1U2D70DMVWH40H4W5	94.0"L x 10.8"W x 3.94"H / 70W 3,190L Up 6,380L Down / White Finish / Frosted Downlight Lens No Uplight Lens / 4000K
LPLIA-96LED1U2D96DMVWH40H4W5	94.0"L x 10.8"W x 3.94"H / 96W 4,310L Up 8,620L Down / White Finish / Frosted Downlight Lens No Uplight Lens / 4000K

Add "EM" for emergency. For continuous run options, see page 26. Also available in 30K, 35K, & 50K.

## Linear Window LED With Direct/Indirect Lighting

This fixture's clean lines are ideal for general lighting for circulation spaces, kitchen islands, and offices

### ITEM NO.

### DESCRIPTION



### Downlight Only

LL-P48LEDD48DMVWHFR40H4W5	48.2"L x 7.7"W x 2.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
LL-P96LEDD96DMVWHFR40H4W5	96.0"L x 7.7"W x 2.0"H / 96W 9,600L / White Finish / Frosted Lens / 4000K

### Uplight & Downlight

LL-P48LED1U2D36DMVWHMW40	48.2"L x 7.7"W x 2.0"H / 36W 1,200L Up 2,400L Down / White Finish / Matte White Lens / 4000K
LL-P48LED1U2D54DMVWHMW40H4W5	48.2"L x 7.7"W x 2.0"H / 54W 1,800L Up 3,600L Down / White Finish / Matte White Lens / 4000K
LL-P96LED1U2D72DMVWHMW40H4W5	96.0"L x 7.7"W x 2.0"H / 72W 2,400L Up 4,800L Down / White Finish / Matte White Lens / 4000K
LL-P96LED1U2D108DMVWHMW40H4W5	96.0"L x 7.7"W x 2.0"H / 108W 3,600L Up 7,200L Down / White Finish / Matte White Lens / 4000K

Add "EM" for emergency. For continuous runs, see page 26. Also available in 30K, 35K, & 50K.



# LINEAR PENDANTS




**3 DIFFERENT  
BODY STYLES!**

## Linear Indirect Lighting (Not Available For Downlight Only)

This sleek, graceful, low-profile fixture features 3 different choices of diffusers. Its high efficiency optics include a specular aluminum reflector that is designed to provide the perfect amount of uplight with a hint of downlight.

ITEM NO.	DESCRIPTION
LI-S48LED2U1D36DMVWH40H4W5	48.0"L x 7.8"W x 2.1"H / 36W 2,400L Up 1,200L Down / White Finish / Matte White Lens / 4000K
LI-S48LED2U1D54DMVWH40H4W5	48.0"L x 7.8"W x 2.1"H / 54W 3,600L Up 1,800L Down / White Finish / Matte White Lens / 4000K
LI-S96LED2U1D72DMVWH40H4W5	96.0"L x 7.8"W x 2.1"H / 72W 4,800L Up 2,400L Down / White Finish / Matte White Lens / 4000K
LI-S96LED2U1D108DMVWH40H4W5	96.0"L x 7.8"W x 2.1"H / 108W 7,200L Up 3,600L Down / White Finish / Matte White Lens / 4000K


Add "EM" for emergency. Also available in 30K, 35K, & 50K.



Perforated (LI)




Matte White Lens (LIS)



Louver (LIB)

Mobern's factory at your fingertips enables you to pick the right powder coat finish, wood finish, or even special rust finish for your application. Experience all the capabilities of customization without the considerable price tag.

**CHOOSE  
YOUR  
FINISH!**




Frost Tower (WD1)




Super Fonthill  
Texture (WD2)




Barnwood Texture  
(WD3)




Silver (SL)




Red (RD)



Iron (IN)



Black (BK)



Bronze (BZ)



Earth (EA1), Corten (CT1), Weatherhead  
Steel (WS1), Rust (RU1)

**MOST FIXTURES ARE  
AVAILABLE IN THESE  
FINISHES. CONSULT FOR  
CUSTOM FINISH OPTIONS.**

# LINEAR PENDANTS



## Louvered 6" Decorative Linear

This direct, louvered, industrial strip makes a bold statement for a modern look.

ITEM NO.	DESCRIPTION
DLV6-48LED48DMVWH40H4W5	48.0"L x 6.0"W x 5.25"H / 48W 5,650L / White Finish / 4000K
DLV6-48LED57DMVWH40H4W5	48.0"L x 6.0"W x 5.25"H / 57W 5,400L / White Finish / 4000K
DLV6-48LED72DMVWH40H4W5	48.0"L x 6.0"W x 5.25"H / 72W 8,200L / White Finish / 4000K
DLV6-96LED48DMVWH40H4W5	96.0"L x 6.0"W x 5.25"H / 48W 5,650L / White Finish / 4000K
DLV6-96LED97DMVWH40H4W5	96.0"L x 6.0"W x 5.25"H / 97W 11,300L / White Finish / 4000K
DLV6-96LED114DMVWH40H4W5	96.0"L x 6.0"W x 5.25"H / 114W 12,800L / White Finish / 4000K
DLV6-96LED144DMVWH40H4W5	96.0"L x 6.0"W x 5.25"H / 144W 16,450L / White Finish / 4000K

Add "EM" for emergency. Change "WH" to "BK", "BZ", "GV", or "SI" for black, bronze, galvanized steel, or silver finish. Also available in 30K, 35K, & 50K.

## Medium Body Direct/Indirect Decorative Strip

This medium body decorative strip gives you the choice of 3 different lens and reflector options for commercial quality configuration with more style.

ITEM NO.	DESCRIPTION
DIS-48LED48DMVFF40XW	48.0"L x 12.5"W x 5.15"H / 48W 4,800L / Fine Fluted Lens Basket / White Steel Reflector / 4000K
DIS-48LED57DMVFF40XW	48.0"L x 12.5"W x 5.15"H / 57W 5,400L / Fine Fluted Lens Basket / White Steel Reflector / 4000K
DIS-48LED72DMVFF40XW	48.0"L x 12.5"W x 5.15"H / 72W 7,000L / Fine Fluted Lens Basket / White Steel Reflector / 4000K
DIS-96LED96DMVFF40XW	96.0"L x 12.5"W x 5.15"H / 96W 9,600L / Fine Fluted Lens Basket / White Steel Reflector / 4000K
DIS-96LED114DMVFF40XW	96.0"L x 12.5"W x 5.15"H / 114W 10,800L / Fine Fluted Lens Basket / White Steel Reflector / 4000K
DIS-96LED144DMVFF40XW	96.0"L x 12.5"W x 5.15"H / 144W 14,000L / Fine Fluted Lens Basket / White Steel Reflector / 4000K

Add "EM" for emergency. Change "FF" to "SW" or "PF" for smooth white or perforated basket. Change "XW" to "XS" or "XP" for full specular mirrored or perforated reflector. Also available in 30K, 35K, & 50K.



## Indirect Linear Strip

This new series provides soft general and directed light from a specially designed indirect source. It is ideal for merchandising applications as well as open offices and circulation spaces.

ITEM NO.	DESCRIPTION
ILS-48LED42DMVWH40H4W5	48"L x 11"W x 8.21"H / 42W 5,000L / White Finish / 4000K
ILS-96LED90DMVWH40H4W5	96"L x 11"W x 8.21"W / 90W 10,000L / White Finish / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Pendant Circular Fixture

Available surface or pendant mounted in 4 different sizes, this statement circle is perfect for lobbies, reception areas, and conference rooms.

ITEM NO.	DESCRIPTION
CIR-P18LED25DMVWH40H5W5	18.90"Dia x 3.14"H / 25W 2,125L / White Finish / Frosted Acrylic Lens / 4000K
CIR-P24LED40DMVWH40H5W5	23.62"Dia x 3.14"H / 40W 3,400L / White Finish / Frosted Acrylic Lens / 4000K
CIR-P36LED90DMVWH40H5W5	35.43"Dia x 3.14"H / 90W 7,650L / White Finish / Frosted Acrylic Lens / 4000K
CIR-P48LED150DMVWH40H5W5	47.24"Dia x 3.14"H / 150W 12,750L / White Finish / Frosted Acrylic Lens / 4000K

Change "WH" to "BK" for black finish. Change "P" to "R" for recessed mount or "S" for surface mount. Also available in 30K & 65K.



**New Product!**

**New Product!**



# Surface Lighting



Mobern has a wide selection of surface-mounted LED products for every application, and many are companions to our extensive recess and pendant mounted fixtures. From flat panels, wraparounds, and channels to wall wash, low-profile “clouds”, and specialty corridor, there is a fixture for every lighting design and application. Each surface mount is available in a variety of sizes, wattages, and lumen outputs. If you don’t see what you need, consult our experts for a custom solution!



For continuous runs, see page 26.

## Linear 2”x 3” Surface Mount (Downlight Only)

Our signature 2” wide surface mount is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

ITEM NO.	DESCRIPTION
L23-S48LED26DMVWHSF40	48”L x 2”W x 3”H / 26W 2,600L / White Finish / Frosted Lens / 4000K
L23-S48LED38DMVWHSF40	48”L x 2”W x 3”H / 38W 3,800L / White Finish / Frosted Lens / 4000K
L23-S48LED45DMVWHSF40	48”L x 2”W x 3”H / 45W 4,500L / White Finish / Frosted Lens / 4000K
L23-S96LED52DMVWHSF40	96”L x 2”W x 3”H / 52W 5,200L / White Finish / Frosted Lens / 4000K
L23-S96LED76DMVWHSF40	96”L x 2”W x 3”H / 76W 7,600L / White Finish / Frosted Lens / 4000K
L23-S96LED90DMVWHSF40	96”L x 2”W x 3”H / 90W 9,000L / White Finish / Frosted Lens / 4000K

Add “EM” for remote mounted emergency. Add “SS” for integral occupancy sensor (adds roughly 3” to fixture length). Consult for other finish options. Also available in 30K, 35K, & 50K.



## Linear 4”x 4” Surface Mount (Downlight Only)

Our signature 4” wide surface mount is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

ITEM NO.	DESCRIPTION
L44-S48LED24DMVWHSF40	48”L x 4”W x 4”H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L44-S48LED48DMVWHSF40	48”L x 4”W x 4”H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-S96LED48DMVWHSF40	96”L x 4”W x 4”H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-S96LED97DMVWHSF40	96”L x 4”W x 4”H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Add “EM” for emergency. Add “SS” for integral occupancy sensor. Consult for other finish options. Also available in 30K, 35K, & 50K.

# SURFACE

## Linear 6"x 6" Surface Mount (Downlight Only)

Our signature 6" wide surface mount is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.



ITEM NO.	DESCRIPTION
L66-S48LED24DMVWHSF40	47.94"L x 5.75"W x 6.0"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L66-S48LED48DMVWHSF40	47.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-S96LED48DMVWHSF40	95.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-S96LED97DMVWHSF40	95.94"L x 5.75"W x 6.0"H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Add "SS" for integral occupancy sensor. Change "SF" to "MW" for matte white lens. Also available in 30K, 35K, & 50K. For continuous runs, see page 26.

## Surface Troffer

This surface troffer with a welded seamless body is perfect for schools, offices, commercial, and public buildings.



ITEM NO.	DESCRIPTION
SRG-22LED24DMV40	2x2 Surface Troffer / 24W 2,600L / 4000K
SRG-22LED28DMV40	2x2 Surface Troffer / 28W 3,000L / 4000K
SRG-22LED35DMV40	2x2 Surface Troffer / 35W 3,600L / 4000K
SRG-14LED30DMV40	1x4 Surface Troffer / 30W 3,585L / 4000K
SRG-14LED48DMV40	1x4 Surface Troffer / 48W 5,385L / 4000K
SRG-24LED35DMV40	2x4 Surface Troffer / 35W 4,345L / 4000K
SRG-24LED48DMV40	2x4 Surface Troffer / 48W 5,900L / 4000K
SRG-24LED57DMV40	2x4 Surface Troffer / 57W 6,735L / 4000K

Add "EM" for emergency. Add "SW" before color temperature for smooth white lens (refer to SRG-LED spec sheet for a full list of lens options). Also available in 30K, 35K, & 50K.

## 9" Rounded Wraparound

This industrial grade wrap is ideal for individual or continuous runs with solid ends for demanding applications.



ITEM NO.	DESCRIPTION
771-48LED32DMVFR40	48.0"L x 9.56"W x 3.19"H / 32W 3,450L / Frosted Lens / 4000K
771-48LED48DMVFR40	48.0"L x 9.56"W x 3.19"H / 48W 4,800L / Frosted Lens / 4000K
771-48LED72DMVFR40	48.0"L x 9.56"W x 3.19"H / 72W 7,200L / Frosted Lens / 4000K
771-96LED48DMVFR40	96.0"L x 9.56"W x 3.19"H / 48W 4,800L / Frosted Lens / 4000K
771-96LED65DMVFR40	96.0"L x 9.56"W x 3.19"H / 65W 7,000L / Frosted Lens / 4000K
771-96LED97DMVFR40	96.0"L x 9.56"W x 3.19"H / 97W 9,600L / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## 7" Wraparound

This 7" wide, low-profile, low-cost, maintenance-free fixture delivers high efficiency in either 2ft. or 4ft. lengths and 2 widths for multiple lumen packages.



ITEM NO.	DESCRIPTION
769-24LED23DMV40	24.0"L x 7.63"W x 3.0"H / 23W 2,750L / Clear Prismatic Lens / 4000K
769-24LED28DMV40	24.0"L x 7.63"W x 3.0"H / 28W 3,280L / Clear Prismatic Lens / 4000K
769-24LED35DMV40	24.0"L x 7.63"W x 3.0"H / 35W 4,330L / Clear Prismatic Lens / 4000K
769-48LED35DMV40	48.0"L x 7.63"W x 3.0"H / 35W 4,370L / Clear Prismatic Lens / 4000K
769-48LED48DMV40	48.0"L x 7.63"W x 3.0"H / 48W 5,750L / Clear Prismatic Lens / 4000K
769-48LED56DMV40	48.0"L x 7.63"W x 3.0"H / 56W 6,570L / Clear Prismatic Lens / 4000K
769W-48LED65DMV40	48.0"L x 13.0"W x 3.0"H Wide Body / 65W 8,100L / Clear Prismatic Lens / 4000K
769W-48LED97DMV40	48.0"L x 13.0"W x 3.0"H Wide Body / 97W 11,500L / Clear Prismatic Lens / 4000K
769W-48LED114DMV40	48.0"L x 13.0"W x 3.0"H Wide Body / 114W 13,140L / Clear Prismatic Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.



Before (T8 Fluorescent)



After (Full LED)

# SURFACE



## 9" Wraparound

This 9" wide, low-profile, low-cost, maintenance-free fixture delivers high efficiency and brightness control in either 2ft. or 4ft. lengths

ITEM NO.	DESCRIPTION
770-48LED32DMVFR40	48.0"L x 9.13"W x 2.63"H / 32W 3,450L / Frosted Lens / 4000K
770-48LED48DMVFR40	48.0"L x 9.13"W x 2.63"H / 48W 5,100L / Frosted Lens / 4000K
770-48LED56DMVFR40	48.0"L x 9.13"W x 2.63"H / 56W 6,000L / Frosted Lens / 4000K
770-48LED72DMVFR40	48.0"L x 9.13"W x 2.63"H / 72W 8,200L / Frosted Lens / 4000K
770-48LED35DMV40	48.0"L x 9.13"W x 2.63"H / 35W 3,800L / Clear Prismatic Lens / 4000K
770-48LED48DMV40	48.0"L x 9.13"W x 2.63"H / 48W 5,100L / Clear Prismatic Lens / 4000K
770-48LED56DMV40	48.0"L x 9.13"W x 2.63"H / 56W 6,019L / Clear Prismatic Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.



## Wide Wraparound

This series features a sleek low-profile, and is ideal for schools, stores, and offices.

ITEM NO.	DESCRIPTION
772-24LED28DMV40	24.0"L x 11.25"W x 3.4"H / 28W 2,800L / Clear Prismatic Lens / 4000K
772-48LED48DMV40	48.0"L x 11.25"W x 3.4"H / 48W 5,000L / Clear Prismatic Lens / 4000K
772-48LED57DMV40	48.0"L x 11.25"W x 3.4"H / 57W 5,700L / Clear Prismatic Lens / 4000K
772-96LED97DMV40	96.0"L x 11.25"W x 3.4"H / 97W 9,600L / Clear Prismatic Lens / 4000K
772-96LED114DMV40	96.0"L x 11.25"W x 3.4"H / 114W 10,800L / Clear Prismatic Lens / 4000K
772W-24LED48DMV40	24.0"L x 15.8"W x 3.4"H / 48W 5,000L / Clear Prismatic Lens / 4000K
772W-48LED72DMV40	48.0"L x 15.8"W x 3.4"H / 72W 8,200L / Clear Prismatic Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.




## Narrow 5" Wraparound

With a narrow cross-section and a full wireway for more uniform light distribution, this wraparound fixture is ideal for hallways and smaller spaces.

ITEM NO.	DESCRIPTION
772N-48LED23DMV40	48.0"L x 5.75"W x 4.6"H / 23W 2,650L / Clear Prismatic Lens / 4000K
772N-48LED32DMV40	48.0"L x 5.75"W x 4.6"H / 32W 3,450L / Clear Prismatic Lens / 4000K
772N-48LED48DMV40	48.0"L x 5.75"W x 4.6"H / 48W 4,800L / Clear Prismatic Lens / 4000K
772N-48LED72DMV40	48.0"L x 5.75"W x 4.6"H / 72W 7,200L / Clear Prismatic Lens / 4000K
772N-96LED48DMV40	96.0"L x 5.75"W x 4.6"H / 48W 5,100L / Clear Prismatic Lens / 4000K
772N-96LED65DMV40	96.0"L x 5.75"W x 4.6"H / 65W 7,000L / Clear Prismatic Lens / 4000K
772N-96LED97DMV40	96.0"L x 5.75"W x 4.6"H / 97W 9,600L / Clear Prismatic Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.



## Corridor Linear

This linear fixture can be ceiling or wall mounted, and is available in a variety of LED combinations and sizes. It is a stylish solution for corridors, aisles, or stairwells.

ITEM NO.	DESCRIPTION
15-24LED24DMV40	24.0"L x 4.62"W x 4.5"H / 24W 2,400L / White Finish / Opal Acrylic Diffuser / 4000K
15-24LED31DMV40	24.0"L x 4.62"W x 4.5"H / 31W 3,100L / White Finish / Opal Acrylic Diffuser / 4000K
15-48LED48DMV40	48.0"L x 4.62"W x 4.5"H / 48W 4,800L / White Finish / Opal Acrylic Diffuser / 4000K
15-48LED62DMV40	48.0"L x 4.62"W x 4.5"H / 62W 6,200L / White Finish / Opal Acrylic Diffuser / 4000K

Also available in 30K, 35K, & 50K.



# SURFACE



*Fits neatly into a corner between ceiling and wall to provide general lighting.*

## Linear Wall Washer

This architectural linear wall wash solution creates the perfect lighting in lobbies and office environments in a sleek, inconspicuous form factor.

ITEM NO.	DESCRIPTION
MW4A-S48LED24DMVWHSF40	48.0"L x 4.0"W x 3.97"H / 24W 2,400L / Frosted Lens / 4000K
MW4A-S48LED48DMVWHSF40	48.0"L x 4.0"W x 3.97"H / 48W 4,800L / Frosted Lens / 4000K
MW4A-S96LED48DMVWHSF40	96.0"L x 4.0"W x 3.97"H / 48W 4,800L / Frosted Lens / 4000K
MW4A-S96LED96DMVWHSF40	96.0"L x 4.0"W x 3.97"H / 96W 9,600L / Frosted Lens / 4000K

Change "S" to "R" for recessed mount. Also available in 30K, 35K, & 50K.



*Ideal for locker rooms, and other high traffic, potentially abusive applications.*

## Triangular Vandal Proof Surface Mount

This heavy duty steel welded body will withstand high impact, and can be wall or ceiling mounted.

ITEM NO.	DESCRIPTION
TVP-24LED25DMVWHFR40	24"L x 12"W x 6"H Tamper Proof / 25W 2,800L / White Finish / Frosted Lens / 4000K
TVP-48LED50DMVWHFR40	48"L x 12"W x 6"H Tamper Proof / 50W 5,600L / White Finish / Frosted Lens / 4000K

Change "FR" to "CL" for clear lens. Also available in 30K, 35K, & 50K.

## Continuous Run Linear Strip Cove Lighting

This fixture contains an integral driver, and is used for general lighting in homes, restaurants, malls, and trains. Its unique plug-and-play system with cord, plug, and butt connector allows you to create continuous runs.



ITEM NO.	DESCRIPTION
CRCS-48LED18MV50	48"L x 1"W x 1"H / 18W 2,250L / 5000K
CRCS-96LED40MV50	96"L x 1"W x 1"H / 40W 5,000L / 5000K
CRCSADJMT	Adjustable And Locking Mounting Bracket Set Of 3

Standard brackets included. Add "CL" after "MV" for clear lens.

## Linkable LED Strip

This miniature 1" strip is ideal for illuminating tight spaces such as coves, displays, and shelf lighting. These can be used individually or linked end to end without cords for continuous runs. Each fixture comes with a 3ft. cord & plug, mini coupler, and mounting clips



ITEM NO.	DESCRIPTION
10M-13LED4E12050	13.5"L x 1.06"W x 0.7"H / 4W 360L / 5000K / 3ft. Cord & Plug, Mini Coupler, & Mounting Clips Included
10M-22LED7E12050	22.5"L x 1.06"W x 0.7"H / 7W 630L / 5000K / 3ft. Cord & Plug, Mini Coupler, & Mounting Clips Included
10M-23LED8E12050	23.8"L x 1.06"W x 0.7"H / 8W 720L / 5000K / 3ft. Cord & Plug, Mini Coupler, & Mounting Clips Included
10M-35LED14E12050	35.6"L x 1.06"W x 0.7"H / 14W 1,260L / 5000K / 3ft. Cord & Plug, Mini Coupler, & Mounting Clips Included
10M-47LED18E12050	47.4"L x 1.06"W x 0.7"H / 18W 1,550L / 5000K / 3ft. Cord & Plug, Mini Coupler, & Mounting Clips Included
10MLED12JOIN	12" Joiner Cord
10MLED24JOIN	24" Joiner Cord
10MLED6JOIN	6" Joiner Cord
10MLEDJBOX	4.0"L x 2.2"W x 1.5"H JBox For Hardwire



Joiner



## Strip With Asymmetric Reflector

Wash the walls with this cost-effective linear strip with asymmetrical reflector.

ITEM NO.	DESCRIPTION
42-24LED18DMV40W35	24"L / 18W 2,590L / 4000K / Asymmetrical Reflector
42-48LED30DMV40W35	48"L / 30W 4,310L / 4000K / Asymmetrical Reflector
42-96LED57DMV40W35	96"L / 57W 7,755L / 4000K / Asymmetrical Reflector

Add "EM" for emergency. Change "W35" to "W65" for curved reflector. For continuous run, see page 26. Consult for other length options. Also available in 30K, 35K, & 50K.




W65 Reflector

# DECORATIVE SURFACE

## Low Profile Cloud

A 3.2" deep, contemporary, opal, rounded diffuser softly and evenly distributes light to create a subtle "cloud" effect on the ceiling. This fixture is more shallow than our "C" fixture on page 40, and can be surface or pendant mounted.



ITEM NO.	DESCRIPTION
CLP-24LED24D120MW40	26.75"L x 9.3"W x 3.2"H / 24W 2,600L / Matte White Lens / 4000K
CLP-48LED42D120MW40	49.75"L x 9.3"W x 3.2"H / 42W 3,819L / Matte White Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Low Profile Cloud 0-10V Dimming

0-10V dimmable version of our low-profile rounded cloud.

ITEM NO.	DESCRIPTION
CLP-24LED20DMVMW40	26.75"L x 9.3"W x 3.2"H / 20W 2,250L / Matte White Lens / 4000K
CLP-24LED24DMVMW40	26.75"L x 9.3"W x 3.2"H / 24W 2,600L / Matte White Lens / 4000K
CLP-24LED28DMVMW40	26.75"L x 9.3"W x 3.2"H / 28W 3,000L / Matte White Lens / 4000K
CLP-48LED40DMVMW40	49.75"L x 9.3"W x 3.2"H / 40W 4,550L / Matte White Lens / 4000K
CLP-48LED48DMVMW40	49.75"L x 9.3"W x 3.2"H / 48W 5,200L / Matte White Lens / 4000K
CLP-48LED57DMVMW40	49.75"L x 9.3"W x 3.2"H / 57W 6,050L / Matte White Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Eclipse (4 Sizes To Match Your Application)

Different end cap options customize this softly rounded eclipse, and add a pleasant architectural effect to any commercial environment.



**End Cap Finish Options:**  
 Silver (SI)  
 Black Marble (BM)  
 Tortoise (TO)  
 Ivory Marble (IM)  
 White Marble (WM)  
 White (WH)



ITEM NO.	DESCRIPTION
MCH-24LED24DMVWHMW40	25.75"L x 9.5"W x 4.5"H / 24W 2,400L / White End Caps / Matte White Lens / 4000K
MCH-24LED36DMVWHMW40	25.75"L x 9.5"W x 4.5"H / 36W 2,900L / White End Caps / Matte White Lens / 4000K
MCH-W24LED48DMVWHMW40	25.75"L x 16.5"W x 5.0"H Wide Body / 48W 4,000L / White End Caps / Matte White Lens / 4000K
MCH-48LED32DMVWHMW40	51.25"L x 9.5"W x 4.5"H / 32W 2,900L / White End Caps / Matte White Lens / 4000K
MCH-48LED48DMVWHMW40	51.25"L x 9.5"W x 4.5"H / 48W 4,000L / White End Caps / Matte White Lens / 4000K
MCH-48LED57DMVWHMW40	51.25"L x 9.5"W x 4.5"H / 57W 5,400L / White End Caps / Matte White Lens / 4000K
MCH-48LED72DMVWHMW40	51.25"L x 9.5"W x 4.5"H / 72W 5,800L / White End Caps / Matte White Lens / 4000K
MCH-W48LED96DMVWHMW40	51.25"L x 16.5"W x 5.0"H Wide Body / 96W 8,000L / White End Caps / Matte White Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Contemporary Cloud

This 3.75" deep designer wraparound fixture has a regressed housing for a floating appearance.




ITEM NO.	DESCRIPTION
MCE-48LED32DMVMW40	50.0"L x 9.75"W x 3.38"H / 32W 3,450L / Matte White Lens / 4000K
MCE-48LED48DMVMW40	50.0"L x 9.75"W x 3.38"H / 48W 4,800L / Matte White Lens / 4000K
MCE-48LED57DMVMW40	50.0"L x 9.75"W x 3.38"H / 57W 5,400L / Matte White Lens / 4000K
MCE-48LED72DMVMW40	50.0"L x 13.75"W x 3.38"H Wide Body / 72W 7,000L / Matte White Lens / 4000K
MCE-48LED97DMVMW40	50.0"L x 13.75"W x 3.38"H Wide Body / 97W 9,600L / Matte White Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

# DECORATIVE SURFACE



C15



C9



C26



Golden Oak Finish



See matching wall, close-to-ceiling, and bath on pages 45, 62 & 64.

## LED Cloud Puff

This contemporary opal acrylic diffuser softly and evenly distributes light at comfortable levels.

ITEM NO.	DESCRIPTION
C26-24LED24DMV40	26.5"L x 26.5"W x 6.0"H / 24W 2,250L / 4000K
C26-24LED28DMV40	26.5"L x 26.5"W x 6.0"H / 28W 2,550L / 4000K
C15-24LED32DMV40	26.5"L x 17.0"W x 6.0"H / 32W 3,450L / 4000K
C15-24LED48DMV40	26.5"L x 17.0"W x 6.0"H / 48W 4,800L / 4000
C9-48LED32DMV40	50.5"L x 11.75"W x 6.0"H / 32W 3,450L / 4000K
C9-48LED48DMV40	50.5"L x 11.75"W x 6.0"H / 48W 4,800L / 4000K
C9-48LED57DMV40	50.5"L x 11.75"W x 6.0"H / 57W 5,500L / 4000K
C9-48LED72DMV40	50.5"L x 11.75"W x 6.0"H / 72W 7,000L / 4000K
C15-48LED65DMV40	50.5"L x 17.0"W x 6.0"H / 65W 7,000L / 4000K
C15-48LED97DMV40	50.5"L x 17.0"W x 6.0"H / 97W 9,600L / 4000K
C15-48LED114DMV40	50.5"L x 17.0"W x 6.0"H / 114W 10,800L / 4000K

C26 also available in 48" length. Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## LED Crown

This versatile fixture provides excellent, even, general illumination with the stylish addition of a crown molding frame that is available in white or golden oak finish.

ITEM NO.	DESCRIPTION
CWN-22LED24DMVWHMW40	2x2 / 25.0"L x 25.0"W x 4.13"H / 24W 2,400L / White Finish / Matte White Lens / 4000K
CWN-22LED28DMVWHMW40	2x2 / 25.0"L x 25.0"W x 4.13"H / 28W 2,700L / White Finish / Matte White Lens / 4000K
CWN-22LED35DMVWHMW40	2x2 / 25.0"L x 25.0"W x 4.13"H / 35W 3,200L / White Finish / Matte White Lens / 4000K
CWN-14LED48DMVWHMW40	1x4 / 48.88"L x 11.5"W x 4.13"H / 48W 4,800L / White Finish / Matte White Lens / 4000K
CWN-14LED57DMVWHMW40	1x4 / 48.88"L x 11.5"W x 4.13"H / 57W 5,400L / White Finish / Matte White Lens / 4000K
CWN-14LED72DMVWHMW40	1x4 / 48.88"L x 11.5"W x 4.13"H / 72W 7,000L / White Finish / Matte White Lens / 4000K
CWN-24LED48DMVWHMW40	2x4 / 48.88"L x 16.75"W x 4.13"H / 48W 4,800L / White Finish / Matte White Lens / 4000K
CWN-24LED57DMVWHMW40	2x4 / 48.88"L x 16.75"W x 4.13"H / 57W 5,400L / White Finish / Matte White Lens / 4000K
CWN-24LED72DMVWHMW40	2x4 / 48.88"L x 16.75"W x 4.13"H / 72W 7,000L / White Finish / Matte White Lens / 4000K

Add "EM" for emergency. Change "WH" to "GO" or "BW" for golden oak or bleached white finish (special order). Also available in 30K, 35K, & 50K.

## LED Spill Ring

Brushed nickel end caps and a white bull-nosed diffuser add deco contemporary style for any commercial or residential application.

ITEM NO.	DESCRIPTION
MDC-48LED32DMVSN40	48.0"L x 11.75"W x 4.5"H / 32W 3,450L / Satin Nickel Finish / 4000K
MDC-48LED48DMVSN40	48.0"L x 11.75"W x 4.5"H / 48W 4,800L / Satin Nickel Finish / 4000K
MDC-48LED57DMVSN40	48.0"L x 11.75"W x 4.5"H / 57W 5,400L / Satin Nickel Finish / 4000K
MDC-48LED72DMVSN40	48.0"L x 11.75"W x 4.5"H / 72W 7,000L / Satin Nickel Finish / 4000K

Add "EM" for emergency. Consult for bronze finish. Also available in 30K, 35K, & 50K.





# Linear Wall

Mobern offers a full palette of complementary wall fixtures for every application in 2", 2.5", 4", 6" wide profiles. Whether the plan calls for a sleek architectural form or a linear strip, we manufacture it to your specifications.



## Wall Linear 2"x 3"

Our signature 2" wide wall mount is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

### ITEM NO.

### DESCRIPTION

#### Direct

L23-W48LED26DMVWHSF40	47"L x 2"W x 3"H / 26W 2,600L / White Finish / Frosted Lens / 4000K
L23-W48LED38DMVWHSF40	47"L x 2"W x 3"H / 38W 3,800L / White Finish / Frosted Lens / 4000K
L23-W48LED45DMVWHSF40	47"L x 2"W x 3"H / 45W 4,500L / White Finish / Frosted Lens / 4000K
L23-W96LED52DMVWHSF40	94"L x 2"W x 3"H / 52W 5,200L / White Finish / Frosted Lens / 4000K
L23-W96LED76DMVWHSF40	94"L x 2"W x 3"H / 76W 7,600L / White Finish / Frosted Lens / 4000K
L23-W96LED90DMVWHSF40	94"L x 2"W x 3"H / 90W 9,000L / White Finish / Frosted Lens / 4000K

#### Direct/Indirect

L23-W48LED1U2D36DMVWHSF40	47"L x 2"W x 3"H / 36W 1,200L Up 2,400L Down / White Finish / Frosted Lens / 4000K
L23-W48LED1U2D54DMVWHSF40	47"L x 2"W x 3"H / 54W 1,800L Up 3,600L Down / White Finish / Frosted Lens / 4000K
L23-W96LED1U2D72DMVWHSF40	94"L x 2"W x 3"H / 72W 2,400L Up 4,800L Down / White Finish / Frosted Lens / 4000K
L23-W96LED1U2D108DMVWHSF40	94"L x 2"W x 3"H / 108W 3,600L Up 7,200L Down / White Finish / Frosted Lens / 4000K

Add "EM" for remote mounted emergency. Add "SS" for integral occupancy sensor (adds roughly 3" to fixture length). Consult for other finish options. Also available in 30K, 35K, & 50K.

## Wall Linear 4"x 4"

Our signature 4" wide wall mount is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

### ITEM NO.

### DESCRIPTION

L44-W48LED24DMVWHSF40	48"L x 4"W x 4"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L44-W48LED48DMVWHSF40	48"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-W96LED48DMVWHSF40	96"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-W96LED96DMVWHSF40	96"L x 4"W x 4"H / 96W 9,600L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Add "SS" for integral occupancy sensor. Consult for other finish options. Also available in 30K, 35K, & 50K.



See page 26 for continuous run options.



# LINEAR WALL

## Wall Linear 4"x 5" Direct/Indirect

Designed specifically for uplight and downlight applications, this 4"x5" wall mount is ideal for corridors, offices, and lobbies where direct/indirect lighting is needed.

### ITEM NO.

### DESCRIPTION

L45-W48LED1U2D36DMVWHSF40	48.0"L x 4.0"W x 5.1"H / 36W 1,200L Up 2,400L Down / White Finish / Frosted Lens / 4000K
L45-W48LED1U2D72DMVWHSF40	48.0"L x 4.0"W x 5.1"H / 72W 2,400L Up 4,800L Down / White Finish / Frosted Lens / 4000K
L45-W96LED1U2D72DMVWHSF40	96.0"L x 4.0"W x 5.1"H / 72W 2,400L Up 4,800L Down / White Finish / Frosted Lens / 4000K
L45-W96LED1U2D108DMVWHSF40	96.0"L x 4.0"W x 5.1"H / 108W 3,600L Up 7,200L Down / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Consult for bronze finish. Also available in 30K, 35K, & 50K.

## Wall Linear 6"x 6"

Our signature 6" wide wall mount is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

### ITEM NO.

### DESCRIPTION

L66-W48LED24DMVWHSF40	47.94"L x 5.75"W x 6.0"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L66-W48LED48DMVWHSF40	47.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-W96LED48DMVWHSF40	95.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-W96LED97DMVWHSF40	95.94"L x 5.75"W x 6.0"H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Add "SS" for integral occupancy sensor. Change "SF" to "MW" for matte white lens. Also available in 30K, 35K, & 50K. For continuous runs, see page 26.

## Wall Linear Window LED With Direct/Indirect Lighting

This fixture's clean lines are ideal for general lighting for circulation spaces.

### ITEM NO.

### DESCRIPTION

Direct	
LL-W48LED48DMVWHMW40	48.2"L x 7.7"W x 2.0"H / 48W 4,800L / White Finish / Matte White Lens / 4000K
LL-W96LED96DMVWHMW40	96.0"L x 7.7"W x 2.0"H / 96W 9,600L / White Finish / Matte White Lens / 4000K
Direct/Indirect	
LL-W48LED1U2D36DMVWHMW40	48.2"L x 7.7"W x 2.0"H / 36W 1,200L Up 2,400L Down / White Finish / Matte White Lens / 4000K
LL-W48LED1U2D54DMVWHMW40	48.2"L x 7.7"W x 2.0"H / 54W 1,800L Up 3,600L Down / White Finish / Matte White Lens / 4000K
LL-W96LED1U2D72DMVWHMW40	96.0"L x 7.7"W x 2.0"H / 72W 2,400L Up 4,800L Down / White Finish / Matte White Lens / 4000K
LL-W96LED1U2D108DMVWHMW40	96.0"L x 7.7"W x 2.0"H / 108W 3,600L Up 7,200L Down / White Finish / Matte White Lens / 4000K

Add "EM" for emergency. Consult for other finish options. For continuous runs, see page 26. Also available in 30K, 35K, & 50K.

## Wall Brackets


Wall brackets provide angled lighting great for bathrooms, kitchens, bulletin boards, and above vanity mirrors.

### ITEM NO.

### DESCRIPTION

74-24LED24DMVCH40	24.0"L x 5.25"W x 3.25"H / 24W 2,250L / Chrome Finish / 4000K
74-48LED48DMVCH40	48.0"L x 5.25"W x 3.25"H / 48W 4,500L / Chrome Finish / 4000K
741-24LED24DMVCH40	24.0"L x 5.5"W x 3.25"H / 24W 2,550L / Chrome Finish / 4000K
741-48LED48DMVCH40	48.0"L x 5.5"W x 3.25"H / 48W 4,500L / Chrome Finish / 4000K
79-24LED12DMVCH40	24.25"L x 4.19"W x 2.56"H / 12W 1,200L / Chrome Finish / 4000K
79-48LED24DMVCH40	48.25"L x 4.19"W x 2.56"H / 24W 2,200L / Chrome Finish / 4000K
791-24LED12DMVCH40	24.38"L x 4.19"W x 2.63"H / 12W 1,100L / Chrome Finish / 4000K
791-48LED24DMVCH40	48.38"L x 4.19"W x 2.63"H / 24W 2,200L / Chrome Finish / 4000K

Consult for EM options. Also available in 30K, 35K, & 50K.



74



741



79



791

# LINEAR WALL

## Linear Indirect Lighting (Uplight Only)

This sleek, graceful, low-profile fixture features 3 different choices of diffusers. Its high efficiency optics include a specular aluminum reflector that is designed to provide the perfect amount of uplight with a hint of downlight.



ITEM NO.	DESCRIPTION
LI-WMS48LED32DMVWH40	48.8"L x 5.0"W x 2.7"H / 32W 3,450L / White Finish / White Lens / 4000K
LI-WMS48LED57DMVWH40	48.8"L x 5.0"W x 2.7"H / 57W 5,400L / White Finish / White Lens / 4000K
LI-WMS96LED97DMVWH40	98.0"L x 5.0"W x 2.7"H / 97W 9,600L / White Finish / White Lens / 4000K
LI-WMS96LED114DMVWH40	98.0"L x 5.0"W x 2.7"H / 114W 10,800L / White Finish / White Lens / 4000K

Add "EM" for emergency. Change "MS" to "MP", "MB", or "MN" for perforated, louvered, or solid body lens. See other finish options on page 33. Also available with up & downlight configuration. Also available in 30K, 35K, & 50K.


## 45° Linear Strip

This 45° linear strip is ideal for interior warehouse, retail, and utility areas. The angled housing makes it perfect for wall and corner applications.



ITEM NO.	DESCRIPTION
CL45-48LED35DMV40	48.0"L x 4.07"W x 2.03"H / 35W 4,900L / 4000K
CL45-48LED48DMV40	48.0"L x 4.07"W x 2.03"H / 48W 6,500L / 4000K
CL45-48LED57DMV40	48.0"L x 4.07"W x 2.03"H / 57W 7,800L / 4000K
CL45-96LED70DMV40	96.0"L x 4.07"W x 2.03"H / 70W 9,800L / 4000K
CL45-96LED97DMV40	96.0"L x 4.07"W x 2.03"H / 97W 13,000L / 4000K
CL45-96LED118DMV40	96.0"L x 4.07"W x 2.03"H / 118W 15,500L / 4000K

Add "EM" for emergency. Change "MS" to "MP", "MB", or "MN" for perforated, louvered, or solid body lens. Also available in 30K, 35K, & 50K.



## 4" Wall Linear

A stylish luminaire with a variety of LED combinations and sizes enhanced by a linear-sided acrylic diffuser.



ITEM NO.	DESCRIPTION
155-24LED24DMVWH40	24.0"L x 4.4"W x 4.5"H / 24W 2,976L / White Finish / 4000K
155-24LED28DMVWH40	24.0"L x 4.4"W x 4.5"H / 28W 3,472L / White Finish / 4000K
155-24LED35DMVWH40	24.0"L x 4.4"W x 4.5"H / 35W 4,340L / White Finish / 4000K
155-48LED30DMVWH40	48.3"L x 4.4"W x 4.5"H / 30W 3,720L / White Finish / 4000K
155-48LED48DMVWH40	48.3"L x 4.4"W x 4.5"H / 48W 5,985L / White Finish / 4000K
155-48LED57DMVWH40	48.3"L x 4.4"W x 4.5"H / 57W 7,068L / White Finish / 4000K
155-48LED72DMVWH40	48.3"L x 4.4"W x 4.5"H / 72W 8,928L / White Finish / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## 4" Up & Down Wall Fixture

This clean, crisp fixture is designed for "over-the-bed" applications. Up and downlight may be controlled with optional dividers, front baffles, and dual drivers. Also available with pull chain.



ITEM NO.	DESCRIPTION
158-24LED1U1D24DMV40BAF	24.2"L x 5.4"W x 4.4"H / 24W 1,330L Up 1,330L Down / 4000K / Front Baffle
158-24LED1U2D36DMV40BAF	24.2"L x 5.4"W x 4.4"H / 36W 1,330L Up 2,660L Down / 4000K / Front Baffle
158-24LED1U1D48DMV40BAF	24.2"L x 5.4"W x 4.4"H / 48W 2,665L Up 2,665L Down / 4000K / Front Baffle
158-24LED2U1D36DMV40BAF	24.2"L x 5.4"W x 4.4"H / 36W 2,660L Up 1,330L Down / 4000K / Front Baffle
158-48LED1U1D48DMV40BAF	48.0"L x 5.4"W x 4.4"H / 48W 2,665L Up 2,665L Down / 4000K / Front Baffle
158-48LED1U2D72DMV40BAF	48.0"L x 5.4"W x 4.4"H / 72W 2,700L Up 5,400L Down / 4000K / Front Baffle
158-48LED1U1D97DMV40BAF	48.0"L x 5.4"W x 4.4"H / 97W 5,330L Up 5,330L Down / 4000K / Front Baffle
158-48LED2U1D72DMV40BAF	48.0"L x 5.4"W x 4.4"H / 72W 5,400L Up 2,700L Down / 4000K / Front Baffle

Add "EM" for emergency. Also available in 30K, 35K, & 50K.



# LINEAR WALL



## Linear Wall Downlight (Ideal For Perimeter Wall Lighting)


This wall-mounted downlight is ideal for lobbies, bathrooms, and office areas and may be installed individually or in group patterns.

ITEM NO.	DESCRIPTION
PWL-48LED30DMVFR40	48.0"L x 4.25"W / 30W 4,100L / Frosted Lens / 4000K
PWL-48LED48DMVFR40	48.0"L x 4.25"W / 48W 6,000L / Frosted Lens / 4000K
PWL-48LED57DMVFR40	48.0"L x 4.25"W / 57W 6,900L / Frosted Lens / 4000K

Also available in 30K, 35K, & 50K.



Modern smart sensors are an integral ultrasonic occupancy sensor to sense motion within a space and automatically turn lights on/off even when the sensor has no direct line of sight to occupants. The sensor's ultrasonic detection operates by transmitting sound waves throughout an area and measuring the speed at which they return. Movement increases the return frequency indicating occupancy. Modern ultrasonic smart sensors provide functions for testing, overriding the fixture "on" and a 72-hour lamp burn-in mode.



## Standard Stairwell With Integrated Sensor

This sleek, wall-mounted fixture with an ultrasonic smart sensor and forward throw optics is ideal for brightening the perimeters of offices or when used as a wall lighting system for corridors.

ITEM NO.	DESCRIPTION
STWR-24LED15DMVWH40SS-xx	24.0"L x 5.6"W x 4.6"H / 15W 2,050L / White Finish / 4000K
STWR-24LED24DMVWH40SS-xx	24.0"L x 5.6"W x 4.6"H / 24W 3,000L / White Finish / 4000K
STWR-48LED48DMVWH40SS-xx	48.0"L x 5.6"W x 4.6"H / 48W 6,000L / White Finish / 4000K
STWR-48LED57DMVWH40SS-xx	48.0"L x 5.6"W x 4.6"H / 57W 6,900L / White Finish / 4000K

## Standard Stairwell With 20% Output & Emergency Unit & Integrated Sensor

STWR-48LED48DMVWH40EMSS-20	48.0 "L x 5.6"W x 4.6"H / 48W 6,000L / White Finish / 4000K / 10W 1,600L Emergency Battery Backup
----------------------------	---

Also available in 30K, 35K, & 50K.

## 3.5" Deep Stairwell Linear With Step Dim Functionality & Integrated Sensor

Featuring ultrasonic smart sensor technology, this wall-mounted fixture is great for "over the bed" applications as well as bath, stairwell, and office applications. Offered with a choice of round or flat lens.

ITEM NO.	DESCRIPTION
155SWR-24LED27SDMV40-xx	24.25"L x 4.5"W x 3.5"H / 27W 2,700L / 4000K
155SWR-48LED36SDMV40-xx	46.25"L x 4.5"W x 3.5"H / 36W 3,600L / 4000K
155SWS-24LED27SDMV40-xx	24.25"L x 4.5"W x 3.5"H / 27W 2,400L / 4000K
155SWS-48LED36SDMV40-xx	46.25"L x 4.5"W x 3.5"H / 36W 3,500L / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## 4.4" Deep Stairwell Linear With Step Dim Functionality & Integrated Sensor

This clean, crisp fixture is designed for "over-the-bed" applications. Up and downlight may be controlled with optional dividers, front baffles, and dual drivers.

ITEM NO.	DESCRIPTION
155SW-24LED15SDMV40-xx	24.0"L x 4.4"W x 4.5"H / 15W 2,050L / 4000K
155SW-24LED24SDMV40-xx	24.0"L x 4.4"W x 4.5"H / 24W 2,990L / 4000K
155SW-48LED48SDMV40-xx	48.0"L x 4.4"W x 4.5"H / 48W 5,985L / 4000K
155SW-48LED57SDMV40-xx	48.0"L x 4.4"W x 4.5"H / 57W 6,855L / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.



155SWR



155SWS



# LINEAR WALL

## LED Spill Ring Bath Multi Color Temperature (Field Adjustable)

Multicolor temperature fixtures have a dip switch that can be adjusted upon installation for 30K, 35K, or 40K.



ITEM NO.	DESCRIPTION
MFLBD-24LED22DMVSNMCT	24.5"L x 5.7"W x 4.5"H / 22W 2,600L / Satin Nickel Finish / 3000K, 3500K, 4000K
MFLBD-36LED31DMVSNMCT	36.5"L x 5.7"W x 4.5"H / 31W 3,100L / Satin Nickel Finish / 3000K, 3500K, 4000K
MFLBD-48LED48DMVSNMCT	48.5"L x 5.7"W x 4.5"H / 48W 5,300L / Satin Nickel Finish / 3000K, 3500K, 4000K

Consult for bronze finish.

## LED Spill Ring Bath

Great fo over-vanity and bath applications!



ITEM NO.	DESCRIPTION
MFLBD-24LED22DMVSN30	24.5"L x 5.7"W x 4.5"H / 22W 2,600L / Satin Nickel Finish / 3000K
MFLBD-36LED31DMVSN30	36.5"L x 5.7"W x 4.5"H / 31W 3,100L / Satin Nickel Finish / 3000K
MFLBD-48LED48DMVSN30	48.5"L x 5.7"W x 4.5"H / 48W 5,300L / Satin Nickel Finish / 3000K

Consult for bronze finish.

## Wall Puff

This contemporary, narrow, white cloud can be mounted horizontally or vertically. The diffuser fully encloses the fixture providing a clean appearance.



ITEM NO.	DESCRIPTION
WP-24LED24DMV40	27.0"L x 6.0"W x 2.75"L / 24W 2,250L / 4000K
WP-48LED48DMV40	51.0"L x 6.0"W x 2.75"L / 48W 4,500L / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Vanity/Bath Fixture

With a variety of different diffuser and end cap options, this end cap bath bar provides a cost-effective, stylish lighting solution.




ITEM NO.	DESCRIPTION
VB-24LED24DMV40SW	25.5"L x 4.75"W x 4.0"H / 24W 2,250L / 4000K / White Smooth Lens / Solid White Finish
VB-24LED28DMV40SW	25.5"L x 4.75"W x 4.0"H / 28W 2,550L / 4000K / White Smooth Lens / Solid White Finish
VB-48LED32DMV40SW	49.5"L x 4.75"W x 4.0"H / 32W 3,250L / 4000K / White Smooth Lens / Solid White Finish
VB-48LED48DMV40SW	49.5"L x 4.75"W x 4.0"H / 48W 4,500L / 4000K / White Smooth Lens / Solid White Finish
VB-48LED57DMV40SW	49.5"L x 4.75"W x 4.0"H / 57W 5,100L / 4000K / White Smooth Lens / Solid White Finish

Change "SW" to "WR", "CR", or "FR" for white ribbed, clear ribbed, or frosted lens. See below for end cap finish options. Also available in 30K, 35K, & 50K.

## End Cap Options:






# Recessed Linear

LED technology allows for maximum light output in a minimal package, perfect for modern interiors. Mobern offers an LED recessed linear fixture for every specification, individual, continuous run, or configuration. These fixtures can be placed in T-bar or hard (flanged or flangeless) ceilings. If the design calls for minimal profile, Mobern has the fixture!




## Choose From 3 Recess Mounting Looks!

**T-Bar Grid Ceiling**  
Specify "R"




End is slightly shorter to accommodate the T-bar grid.

**Hard Ceiling -  
Sheetrock Flanged Version**  
Specify "RF"



**Hard Ceiling -  
Sheetrock Flangeless Version**  
Option 1: Install before sheetrock  
Specify "RRXXX"  
XXX - Depth of sheetrock  
Option 2: Install after sheetrock  
RRPF - Perforated flange to mud to



New perforated flange  
1/4" below ceiling to  
mud to (RRPF)



# RECESSED LINEAR



L23RRXXX

## Recessed Linear 2"x 3"

Our signature 2" wide fixture packs a large punch of light, and allows for application specific customization in T-bar, hard deck, or specialty ceilings.

ITEM NO.	DESCRIPTION
L23-R48LED26DMVWHSF40	47.45"L x 2.0"W x 3.0"H / 26W 2,600L / White Finish / Frosted Lens / 4000K
L23-R48LED38DMVWHSF40	47.45"L x 2.0"W x 3.0"H / 38W 3,800L / White Finish / Frosted Lens / 4000K
L23-R48LED45DMVWHSF40	47.45"L x 2.0"W x 3.0"H / 45W 4,500L / White Finish / Frosted Lens / 4000K
L23-R96LED52DMVWHSF40	95.45"L x 2.0"W x 3.0"H / 52W 5,200L / White Finish / Frosted Lens / 4000K
L23-R96LED76DMVWHSF40	95.45"L x 2.0"W x 3.0"H / 76W 7,600L / White Finish / Frosted Lens / 4000K
L23-R96LED90DMVWHSF40	95.45"L x 2.0"W x 3.0"H / 90W 9,000L / White Finish / Frosted Lens / 4000K

Use "L23R" for T-Bar grid ceiling, "L23RF" for flanged, and "L23RR(XXX)" for flangeless hard ceiling (xxx) for sheetrock depth. Also available in 30K, 35K, & 50K.

## Recessed Linear 2.5"x 3.3"

Our signature 2.5" wide recessed fixture is great for corridors, offices, and lobbies.

ITEM NO.	DESCRIPTION
LD23-R48LED26DMVWHSF40	47.32"L x 2.38"W x 3.35"H / 26W 2,600L / White Finish / Frosted Lens / 4000K
LD23-R48LED38DMVWHSF40	47.32"L x 2.38"W x 3.35"H / 38W 3,800L / White Finish / Frosted Lens / 4000K
LD23-R48LED45DMVWHSF40	47.32"L x 2.38"W x 3.35"H / 45W 4,500L / White Finish / Frosted Lens / 4000K
LD23-R96LED52DMVWHSF40	96.0"L x 2.38"W x 3.35"H / 52W 5,200L / White Finish / Frosted Lens / 4000K
LD23-R96LED76DMVWHSF40	96.0"L x 2.38"W x 3.35"H / 76W 7,600L / White Finish / Frosted Lens / 4000K
LD23-R96LED90DMVWHSF40	96.0"L x 2.38"W x 3.35"H / 90W 9,000L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Use "LD23R" for T-Bar grid ceiling, "LD23RF" for flanged, and "LD23RR(XXX)" for flangeless hard ceiling (XXX) for sheetrock depth. Also available in 30K, 35K, & 50K.

## Recessed Linear 4"x 4"

Our signature 4" wide recessed fixture is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

ITEM NO.	DESCRIPTION
L44-R48LED24DMVWHSF40	48"L x 4"W x 4"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L44-R48LED48DMVWHSF40	48"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-R96LED48DMVWHSF40	96"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-R96LED97DMVWHSF40	96"L x 4"W x 4"H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Use "L44R" for T-Bar grid ceiling, "L44RF" for flanged, and "L44RR(XXX)" for flangeless hard ceiling (xxx) for sheetrock depth. For regressed white lens change "SF" to "MW". Add "SS" for integrated sensor. Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Recessed Linear 6"x 6"

Our signature 6" wide recessed fixture is great for corridors, offices, and lobbies. The snap-in frosted lens hides LED arrays and provides excellent glare control.

ITEM NO.	DESCRIPTION
L66-R48LED48DMVWHSF40	47.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-R96LED48DMVWHSF40	95.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-R96LED97DMVWHSF40	95.94"L x 5.75"W x 6.0"H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Use "L66R" for T-Bar grid ceiling, "L66RF" for flanged, and "L66RR(XXX)" for flangeless hard ceiling (xxx) for sheetrock depth. For regressed white lens change "SF" to "MW". Add "SS" for integrated sensor. Add "EM" for emergency. Also available in 30K, 35K, & 50K.



Consult for 2ft. & other custom lengths!

### Specify Continuous Runs

To specify continuous runs, identify the fixtures for the beginning ("B"), for the joiner(s) ("J"), and for the end of the run ("E") with these letter designations at the end of the part number. The fixtures will include the necessary electrical harnesses and mechanical accessories for the joining of multiple fixtures.

### Dimming to 1%

Standard DMV provides dimming to 10% intensity. For dim to 1%, up to 57 watts, change DMV to DIMV.

# RECESSED LINEAR



Shown without lens.

Specially designed reflector provides asymmetrical light distribution ideal for economical wall washing.

## Recessed Linear Wall Wash 4"x 4"

This economical 4" recessed wall wash provides an asymmetrical light distribution and is ideal for offices or lobby areas.

ITEM NO.	DESCRIPTION
L44-R48LED24DMVWHSF40WW	48"L x 4"W x 4"H / 24W 2,400L / White Finish / Frosted Lens / 4000K
L44-R48LED48DMVWHSF40WW	48"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-R96LED48DMVWHSF40WW	96"L x 4"W x 4"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L44-R96LED97DMVWHSF40WW	96"L x 4"W x 4"H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Add "SS" for integrated sensor. Add "EM" for emergency. Available with or without flange, Also available in 30K, 35K, & 50K.

## Recessed Linear Wall Wash 6"x 6"

This economical 6" recessed wall wash provides an asymmetrical light distribution, and is ideal for offices or lobby areas.

ITEM NO.	DESCRIPTION
L66-R48LED48DMVWHSF40WW	47.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-R96LED48DMVWHSF40WW	95.94"L x 5.75"W x 6.0"H / 48W 4,800L / White Finish / Frosted Lens / 4000K
L66-R96LED97DMVWHSF40WW	95.94"L x 5.75"W x 6.0"H / 97W 9,600L / White Finish / Frosted Lens / 4000K

Add "SS" for integrated sensor. Add "EM" for emergency. Available with or without flange, Also available in 30K, 35K, & 50K.



Shown without lens.



Internal Reflector

## Recessed 4"x 4" Indirect Linear

The unique structure of this fixture, with no horizontal lens or diffuser, stands out among other linear style pendants. Specially engineered LED arrays lay discretely on the bottom edge of the linear channel to brightly illuminate the barreled reflector and provide a soft downward spread of light.

ITEM NO.	DESCRIPTION
L44IR-R24LED25DMVWH40	24.0"L x 4.02"W x 4.02"H / 25W 2,000L / White Finish / 4000K
L44IR-R48LED50DMVWH40	48.18"L x 4.02"W x 4.02"H / 50W 4,000L / White Finish / 4000K
L44IR-R96LED100DMVWH40	96.0"L x 4.02"W x 4.02"H / 100W 8,000L / White Finish / 4000K

Use "L44IRR" for T-Bar grid ceiling, "L44IRRF" for flanged, and "L44IRR(XXX)" for flangeless hard ceiling (xxx) for sheetrock depth. Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Recessed Open Linear (Ideal For Retail Stores)

This recessed channel outperforms traditional troffers and strip fixtures by maximizing comfortable, glare-free, light levels for general merchandising environments.

ITEM NO.	DESCRIPTION
ROL-48LED23DMV40	47.96"L x 11.71"W x 5.45"H / 23W 3,000L / 4000K
ROL-48LED48DMV40	47.96"L x 11.71"W x 5.45"H / 48W 5,650L / 4000K
ROL-96LED48DMV40	95.92"L x 11.71"W x 5.45"H / 48W 5,650L / 4000K
ROL-96LED85DMV40	95.92"L x 11.71"W x 5.45"H / 85W 11,000L / 4000K

Also available in 30K, 35K, & 50K.



# RECESSED LINEAR

Series AIOCLF provides an elegant and uniform line of light only 1.5" wide to seamlessly blend into a hard ceiling, normally sheetrock. With the choice of either a crisp, white flange or flangeless appearance, the AIOCLF has versatility for different design concepts. The flangeless version shows only a narrow lens, and includes a specially-designed mud-in flange adjustable to 1/8", 1/2" or 5/8" to match sheetrock thickness and mud-in methods. The AIOCLF comes in 4ft. or 8ft. lengths, and can be joined together for continuous runs.



**New Product!**



### Rough In & Trim System

Separate housing and installs easily during rough-in. LED trim installs quickly during trim out with innovative magnetic system.



125



250



375




500

## All-In-One Recessed Linear Channel

ITEM NO.	DESCRIPTION
AIOCLF-RF48LED30DMVWH40	50.08"L x 3.25"W x 2.6"H With Flange / 30W 3,000L / White Finish / 4000K
AIOCLF-RR48LED30DMVWH40	48.43"L x 3.15"W x 2.6"H Flangeless / 30W 3,000L / White Finish / 4000K
AIOCLF-RF96LED60DMVWH40	98.07"L x 3.25"W x 2.6"H With Flange / 60W 6,000L / White Finish / 4000K
AIOCLF-RR96LED60DMVWH40	96.42"L x 3.15"W x 2.6"H Flangeless / 60W 6,000L / White Finish / 4000K

Also available in 30K, 35K, & 50K.


The **1 2 3** kit is a uniquely designed AIOCLF kit including a 3ft., 2ft., and 1ft. channel that can be used together to make one 6ft. channel or staggered individually for a modern cascading aesthetic. The 3ft. channel has an integral driver as well as a unique plug and play wiring system to power the 1ft. and 2ft. channels with a 6ft. cord (consult for longer cords).



## All-In-One Recessed Linear Channel

ITEM NO.	DESCRIPTION
AIOCLF-RFKITDMVWH30	Recessed Flanged 3 Piece Set 38.1", 26.1", & 14.1"L x 3.2"W x 2.6"H (For Piece With Driver) 1.4"H (For Pieces Without Driver) / 45W 4,200L / White Finish / 3000K
AIOCLF-RFKITDMVWH40	Recessed Flanged 3 Piece Set 38.1", 26.1", & 14.1"L x 3.2"W x 2.6"H (For Piece With Driver) 1.4"H (For Pieces Without Driver) / 45W 4,200L / White Finish / 4000K
AIOCLF-RRKITDMVWH30	Recessed Flangeless 3 Piece Set 36.4", 24.4"W, & 12.4"L x 3.15"W x 2.6"H (For Piece With Driver) 1.4"H (For Pieces Without Driver) / 45W 4,200L / White Finish / 3000K
AIOCLF-RRKITDMVWH40	Recessed Flangeless 3 Piece Set 36.4", 24.4"W, & 12.4"L x 3.15"W x 2.6"H (For Piece With Driver) 1.4"H (For Pieces Without Driver) / 45W 4,200L / White Finish / 3000K

Also available in 30K, 35K, & 50K.





# RECESSED LINEAR



## Recessed Linear 1.93" Width With Flange & Remote Driver

Great for micro-illumination applications when you need to place light precisely!

ITEM NO.	DESCRIPTION
LLCSR-47LED42SA40	47.0"L x 1.93"W x 1.26"H / 42W 2,488L / Satin Aluminum Finish / 4000K
LLCSR-96LED83SA40	96.0"L x 1.93"W x 1.26"H / 83W 4,976L / Satin Aluminum Finish / 4000K

Order driver separately. 10 watts per foot. Also available in 30K.



## Recessed Linear 2.16" Width With Flange & Remote Driver

This fixture has all the benefits of our LLCSR but with a slightly wider (2.16") profile and additional flange and pattern accessories.

ITEM NO.	DESCRIPTION
LLCFR-48LED24SA30	47.24"L x 2.16"W x 1.38"H / 24W 2,125L / Satin Aluminum Finish / 3000K
LLCFR-48LED24SA40	47.24"L x 2.16"W x 1.38"H / 24W 2,125L / Satin Aluminum Finish / 4000K
LLCFR-96LED49SA30	96.46"L x 2.16"W x 1.38"H / 49W 4,335L / Satin Aluminum Finish / 3000K
LLCFR-96LED49SA40	96.46"L x 2.16"W x 1.38"H / 49W 4,335L / Satin Aluminum Finish / 3000K

Consult for custom configurations and ordering. Also available in 40K.

## LLCFR Pattern Options

Configure recessed squares, triangles, rectangles, or any pattern including up a wall and across a ceiling.



Flat Corner



Inside Corner



Outside Corner



Flat "T"



X-Cross



Screw Clip



Spring Clip

ITEM NO.	DESCRIPTION
LLCFRJOINER	Joiner Spline for LLCFR Extrusion
LLCFRCORNER30	LLCFR 90 Degree Flat Corner 3000K
LLCFRCORNER40	LLCFR 90 Degree Flat Corner 4000K
LLCFRIS9030	LLCFR 90 Degree Inside Corner 3000K
LLCFRIS9040	LLCFR 90 Degree Inside Corner 4000K
LLCFROS9030	LLCFR 90 Degree Outside Corner 3000K
LLCFROS9040	LLCFR 90 Degree Outside Corner 4000K
LLCFRTEE30	LLCFR Flat "T" 3000K
LLCFRTEE40	LLCFR Flat "T" 4000K
LLCFRCROSS30	LLCFR Flat X-CROSS 3000K
LLCFRCROSS40	LLCFR FLAT X-CROSS 4000K
LLCFRRECCLIP	LLCFR Recessed Screw Clip
LLCFRSPRINGCLIP	LLCFR Butterfly Spring Clip Set (2)

## Remote Driver


ITEM NO.	DESCRIPTION
LEDD-MDCV24V60-120VHW	Magniture Magnetic Driver 60W 24VDC Encased
LEDD-MDCV24V96-120VHW	Magniture Magnetic Driver 96W 24VDC Encased
LEDD-MDCV24V150-120VHW	Magniture Magnetic Driver 150W 24VDC Encased

See page 31 for other drivers and wattages.



# RECESSED LINEAR

The PER-LED is a cost-effective solution where cove lighting is desired. Create an elegant wash of ambient and vertical illumination between the wall and ceiling planes in offices, hallways, conference rooms, and medical facilities. It is available in 2, 4, 6, and 8 foot sections along with telescoping and corner options that can be combined for longer runs a 4" regressed optics. This perimeter lighting system eliminates the need for a more costly "built-in-place" solution.



## Recessed Perimeter Light

ITEM NO.	DESCRIPTION
PER-W44R24LED16DMVSF40	24"L x 4"W x 4"H / 16W 1,600L / Frosted Lens / 4000K
PER-W44R48LED32DMVSF40	48"L x 4"W x 4"H / 32W 3,200L / Frosted Lens / 4000K
PER-W44R72LED48DMVSF40	72"L x 4"W x 4"H / 48W 4,800L / Frosted Lens / 4000K
PER-W44R96LED64DMVSF40	96"L x 4"W x 4"H / 64W 6,400L / Frosted Lens / 4000K
PER-W46R24LED16DMVSF40	24"L x 4"W x 6"H / 16W 1,600L / Frosted Lens / 4000K
PER-W46R48LED32DMVSF40	48"L x 4"W x 6"H / 32W 3,200L / Frosted Lens / 4000K
PER-W46R72LED48DMVSF40	72"L x 4"W x 6"H / 48W 4,800L / Frosted Lens / 4000K
PER-W46R96LED64DMVSF40	96"L x 4"W x 6"H / 64W 6,400L / Frosted Lens / 4000K

Add "EM" for emergency. Use "PERW" wall bracket for drywall installation, and "PERTR" threaded rod for grid ceiling installation. Change "R" to "RF" for recessed flange. Also available in 30K, 35K, & 50K.



Add "-T" to the end of the part number for telescoping option.

## New Product!



# RECESSED



## Sky Bay (Innovative Recessed Shroud & Flat Panels Combined)

This slim, elegant design offers a skylight appearance with a standard flat panel.

ITEM NO.	DESCRIPTION
SKB-22LED40DMVWH40	23.75"L x 23.75"W x 4.72"H / 40W 5,000L / White Finish / 4000K
SKB-14LED40DMVWH40	47.50"L x 11.79"W x 4.69"H / 40W 5,000L / White Finish / 4000K
SKB-24LED50DMVWH40	47.67"L x 23.75"W x 4.69"H / 50W 6,250L / White Finish / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.



## Sky Bay Accessory (Flat Panel Sold Separately)

Transform any LED edge-lit panel into a specification-grade fixture with the addition of this sleek shroud.

ITEM NO.	DESCRIPTION
SKBKT22	2x2 / 23.95"L x 23.95"W x 3.68"H
SKBKT14	1x4 / 47.65"L x 12"W x 3.68"H
SKBKT24	2x4 / 47.86"L x 23.95"W x 3.68"H



*Specify a custom color to add visual interest or to support corporate branding!*

# RECESSED



Back of fixture

## LED Edge Lit Flat Panel (External Driver)

A popular look for many applications including schools, retail, hospitality, and healthcare spaces.

ITEM NO.	DESCRIPTION
MFPELA-14LED36DMV40	1x4 / 47.75"L x 11.73"W x 1.45"H / 36W 4,660L / 4000K
MFPELA-22LED36DMV40	2x2 / 23.74"L x 23.74"W x 1.45"H / 36W 4,810L / 4000K
MFPELA-24LED50DMV40	2x4 / 47.75"L x 23.74"W x 1.45"H / 50W 6,500L / 4000K

### Hanging Kit

A-MFPELA-HK	59" Aircraft Cable Kit / 4 Pieces Required For 2x2 and 1x4, 6 Pieces Required For 2x4
-------------	---

Add "EM" for emergency. Also available in 30K, 35K, & 50K.


## Backlit Flat Panels Coming Soon!

## Surface Shroud (Flat Panel Sold Separately)

ITEM NO.	DESCRIPTION
SMKT22-MFPEL	2x2 / 24"L x 24"W x 3"H
SMKT14-MFPEL	1x4 / 48"L x 12"W x 3"H
SMKT24-MFPEL	2x4 / 48"L x 24"W x 3"H



Create custom configurations with our new flex mounting system for flat panels FMS-FP.



## LED Center Basket


Featuring an extruded lens, this volumetric recessed luminaire provides smooth and uniform ambient lighting for all commercial/industrial buildings with recessed configurations.

ITEM NO.	DESCRIPTION
RDIS-22LED28DMVFR40	2x2 / 24.0"L x 24.0"W x 3.26"H / 28W 3,498L / Frosted Lens / 4000K
RDIS-22LED35DMVFR40	2x2 / 24.0"L x 24.0"W x 3.26"H / 35W 4,200L / Frosted Lens / 4000K
RDIS-14LED32DMVFR40	1x4 / 47.0"L x 12.0"W x 3.26"H / 32W 3,620L / Frosted Lens / 4000K
RDIS-14LED48DMVFR40	1x4 / 47.0"L x 12.0"W x 3.26"H / 48W 5,450L / Frosted Lens / 4000K
RDIS-24LED48DMVFR40	2x4 / 47.0"L x 24.0"W x 3.26"H / 48W 5,448L / Frosted Lens / 4000K
RDIS-24LED57DMVFR40	2x4 / 47.0"L x 24.0"W x 3.26"H / 57W 5,825L / Frosted Lens / 4000K

### Air Return

RDISA-22LED28DMVFR40	2x2 / 24.0"L x 24.0"W x 3.26"H / 28W 3,498L / Frosted Lens / 4000K
RDISA-22LED35DMVFR40	2x2 / 24.0"L x 24.0"W x 3.26"H / 35W 4,200L / Frosted Lens / 4000K
RDISA-24LED48DMVFR40	2x4 / 47.0"L x 24.0"W x 3.26"H / 48W 5,448L / Frosted Lens / 4000K
RDISA-24LED57DMVFR40	2x4 / 47.0"L x 24.0"W x 3.26"H / 57W 5,825L / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.



Air return allows ceiling air to be recirculated through the plenum for modification of the environment in the area.



# RECESSED

## LED Center Basket With Integrated Smart Sensor

Featuring an extruded lens and an integral occupancy sensor, this volumetric recessed luminaire provides smooth and uniform ambient lighting for all commercial/industrial buildings with recessed configurations.



Available with a variety of sensors. Consult for Leviton Intellect sensor and control system. For additional sensor options, see pages 4 & 5.

### ITEM NO.

### DESCRIPTION

ITEM NO.	DESCRIPTION
RDIS-22LED28DMVFR40SS	2x2 / 24.0"L x 24.0"W x 3.26"H / 28W 3,498L / Frosted Lens / 4000K
RDIS-22LED35DMVFR40SS	2x2 / 24.0"L x 24.0"W x 3.26"H / 35W 4,200L / Frosted Lens / 4000K
RDIS-14LED32DMVFR40SS	1x4 / 47.0"L x 12.0"W x 3.26"H / 32W 3,620L / Frosted Lens / 4000K
RDIS-14LED48DMVFR40SS	1x4 / 47.0"L x 12.0"W x 3.26"H / 48W 5,450L / Frosted Lens / 4000K
RDIS-24LED48DMVFR40SS	2x4 / 47.0"L x 24.0"W x 3.26"H / 48W 5,448L / Frosted Lens / 4000K
RDIS-24LED57DMVFR40SS	2x4 / 47.0"L x 24.0"W x 3.26"H / 57W 5,825L / Frosted Lens / 4000K

### Air Return

ITEM NO.	DESCRIPTION
RDISA-22LED28DMVFR40SS	2x2 / 24.0"L x 24.0"W x 3.26"H / 28W 3,498L / Frosted Lens / 4000K
RDISA-22LED35DMVFR40SS	2x2 / 24.0"L x 24.0"W x 3.26"H / 35W 4,200L / Frosted Lens / 4000K
RDISA-24LED48DMVFR40SS	2x4 / 47.0"L x 24.0"W x 3.26"H / 48W 5,448L / Frosted Lens / 4000K
RDISA-24LED57DMVFR40SS	2x4 / 47.0"L x 24.0"W x 3.26"H / 57W 5,825L / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Economy Center Basket

This value, spec-grade, center basket creates even light distribution from floor to ceiling while still providing a soft "skylight" appearance.



Surface mount almost any recessed fixture by adding "S" prefix!

### ITEM NO.

### DESCRIPTION

ITEM NO.	DESCRIPTION
RDISE-22LED20DMVFR40	2x2 / 24.0"L x 24.0"W x 3.26"H / 20W 2,537L / Frosted Lens / 4000K
RDISE-22LED30DMVFR40	2x2 / 24.0"L x 24.0"W x 3.26"H / 30W 3,606L / Frosted Lens / 4000K
RDISE-14LED35DMVFR40	1x4 / 48.0"L x 12.0"W x 3.26"H / 35W 4,580L / Frosted Lens / 4000K
RDISE-14LED57DMVFR40	1x4 / 48.0"L x 12.0"W x 3.26"H / 57W 7,020L / Frosted Lens / 4000K
RDISE-24LED35DMVFR40	2x4 / 48.0"L x 24.0"W x 3.26"H / 35W 4,685L / Frosted Lens / 4000K
RDISE-24LED48DMVFR40	2x4 / 48.0"L x 24.0"W x 3.26"H / 48W 6,155L / Frosted Lens / 4000K
RDISE-24LED57DMVFR40	2x4 / 48.0"L x 24.0"W x 3.26"H / 57W 7,212L / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.



# RECESSED



## Decorative Center Basket

An extruded optically-designed acrylic center lens with a softening mesh overlay provides low glare, and is ideal for offices, hospitals, and schools

ITEM NO.	DESCRIPTION
SKY-22LED20DMV40	2x2 / 23.8"L x 23.8"W x 2.9"H / 20W 2,455L / Standard Linear Ribbed Acrylic Lens / 4000K
SKY-22LED36DMV40	2x2 / 23.8"L x 23.8"W x 2.9"H / 36W 4,190L / Standard Linear Ribbed Acrylic Lens / 4000K
SKY-24LED28DMV40	2x4 / 47.8"L x 23.8"W x 2.9"H / 28W 3,600L / Standard Linear Ribbed Acrylic Lens / 4000K
SKY-24LED60DMV40	2x4 / 47.8"L x 23.8"W x 2.9"H / 60W 7,355L / Standard Linear Ribbed Acrylic Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Curve Lit Sides Center Basket

Unique dual lit side lenses create a luminous housing with excellent visual comfort.

ITEM NO.	DESCRIPTION
RGCRV-22LED28DMVRL40	2x2 / 24"L x 24"W x 4"H / 28W 2,400L / Ribbed Linear Lens / 4000K
RGCRV-22LED35DMVRL40	2x2 / 24"L x 24"W x 4"H / 35W 3,200L / Ribbed Linear Lens / 4000K
RGCRV-24LED32DMVRL40	2x4 / 48"L x 24"W x 4"H / 32W 3,450L / Ribbed Linear Lens / 4000K
RGCRV-24LED48DMVRL40	2x4 / 48"L x 24"W x 4"H / 48W 4,800L / Ribbed Linear Lens / 4000K
RGCRV-24LED57DMVRL40	2x4 / 48"L x 24"W x 4"H / 57W 5,400L / Ribbed Linear Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Dual Basket

A dual basket design creates a "skylight" appearance with a wider distribution.

ITEM NO.	DESCRIPTION
RDISD-22LED24DMVFR40	2x2 / 23.68"L x 23.68"W x 3.25"H / 24W 3,000L / Frosted Lens / 4000K
RDISD-22LED28DMVFR40	2x2 / 23.68"L x 23.68"W x 3.25"H / 28W 3,500L / Frosted Lens / 4000K
RDISD-22LED35DMVFR40	2x2 / 23.68"L x 23.68"W x 3.25"H / 35W 4,375L / Frosted Lens / 4000K
RDISD-24LED48DMVFR40	2x4 / 47.67"L x 23.68"W x 3.25"H / 48W 6,000L / Frosted Lens / 4000K
RDISD-24LED57DMVFR40	2x4 / 47.67"L x 23.68"W x 3.25"H / 57W 7,125L / Frosted Lens / 4000K
RDISD-24LED60DMVFR40	2x4 / 47.67"L x 23.68"W x 3.25"H / 60W 7,500L / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, & 50K.

## Perimeter Lighting

The RWW offers uniform, vertical, surface lighting for commercial and retail environments.

ITEM NO.	DESCRIPTION
RWW-24LED24DMV40	24.0"L x 10.62"W x 4.5"H / 24W 2,400L / 4000K
RWW-24LED35DMV40	24.0"L x 10.62"W x 4.5"H / 35W 3,400L / 4000K
RWW-48LED24DMV40	48.0"L x 10.62"W x 4.5"H / 24W 2,400L / 4000K
RWW-48LED48DMV40	48.0"L x 10.62"W x 4.5"H / 48W 4,800L / 4000K
RWW-48LED57DMV40	48.0"L x 10.62"W x 4.5"H / 57W 5,700L / 4000K
RWW-48LED72DMV40	48.0"L x 10.62"W x 4.5"H / 72W 7,200L / 4000K

Also available in 30K, 35K, & 50K.

## Recessed Parabolic

When glare control and cut-off are important, this deep cell parabolic troffer delivers!

ITEM NO.	DESCRIPTION
RP-229LED24DMV40	2x2 / 23.75"L x 23.75"W x 5.50"H / 9 Cell / 24W 2,050L / 4000K
RP-229LED42DMV40	2x2 / 23.75"L x 23.75"W x 5.50"H / 9 Cell / 42W 3,300L / 4000K
RP-229LED54DMV40	2x2 / 23.75"L x 23.75"W x 5.50"H / 9 Cell / 54W 4,430L / 4000K
RP-2418LED48DMV40	2x4 / 47.75"L x 23.75"W x 5.50"H / 18 Cell / 48W 3,650L / 4000K
RP-2418LED60DMV40	2x4 / 47.75"L x 23.75"W x 5.50"H / 18 Cell / 60W 5,420L / 4000K
RP-2418LED85DMV40	2x4 / 47.75"L x 23.75"W x 5.50"H / 18 Cell / 85W 7,350L / 4000K

Add "EM" for emergency. For frosted overlay to hide LED's, add "OL" at the end of part number. Consult for louvered options. Also available in 30K, 35K, & 50K.



# RECESSED



Update your look for the standard troffer with the RAV-LED.

## 4 Different Lens Options!

### Recessed Architectural Volumetric With Multiple Lens Options

Give your classic troffer design the architectural, modern appearance of a center basket with this specially designed troffer with 4 unique lens options!

ITEM NO.	DESCRIPTION
RAV-22LED24DMVA40	2x2 / 23.75"L x 23.75"W x 3.75"H / 24W 2,600L / Curved Ribbed Center Lens / 4000K
RAV-22LED28DMVA40	2x2 / 23.75"L x 23.75"W x 3.75"H / 28W 3,000L / Curved Ribbed Center Lens / 4000K
RAV-22LED35DMVA40	2x2 / 23.75"L x 23.75"W x 3.75"H / 35W 3,600L / Curved Ribbed Center Lens / 4000K
RAV-24LED35DMVA40	2x4 / 47.75"L x 23.75"W x 3.75"H / 35W 4,345L / Curved Ribbed Center Lens / 4000K
RAV-24LED45DMVA40	2x4 / 47.75"L x 23.75"W x 3.75"H / 45W 5,500L / Curved Ribbed Center Lens / 4000K
RAV-24LED57DMVA40	2x4 / 47.75"L x 23.75"W x 3.75"H / 57W 6,735L / Curved Ribbed Center Lens / 4000K
RAV-24LED72DMVA40	2x4 / 47.75"L x 23.75"W x 3.75"H / 72W 8,700L / Curved Ribbed Center Lens / 4000K

Add "EM" for emergency. Add "SSM" for microwave sensor. Change "A" after DMV to one of the lens options below for a different lens style. Also available in 30K, 35K, & 50K.

Curved Ribbed Center Lens



A

Curved Body Troffer Lens



B

Flat Center Lens



C

Concave Body Troffer Lens



D

### LED Air Handling Troffer

Air handling allows ceiling air to be recirculated through the plenum for modification of the environment in the area.

ITEM NO.	DESCRIPTION
RGAIR-22LED24DMV40	2x2 / 23.75"L x 23.75"W x 3.75"H / 24W 2,340L / Standard .100 Acrylic Prismatic Lens / 4000K
RGAIR-22LED28DMV40	2x2 / 23.75"L x 23.75"W x 3.75"H / 28W 2,800L / Standard .100 Acrylic Prismatic Lens / 4000K
RGAIR-22LED35DMV40	2x2 / 23.75"L x 23.75"W x 3.75"H / 35W 3,300L / Standard .100 Acrylic Prismatic Lens / 4000K
RGAIR-24LED35DMV40	2x4 / 47.75"L x 23.75"W x 3.75"H / 35W 4,130L / Standard .100 Acrylic Prismatic Lens / 4000K
RGAIR-24LED45DMV40	2x4 / 47.75"L x 23.75"W x 3.75"H / 45W 5,225L / Standard .100 Acrylic Prismatic Lens / 4000K
RGAIR-24LED57DMV40	2x4 / 47.75"L x 23.75"W x 3.75"H / 57W 6,400L / Standard .100 Acrylic Prismatic Lens / 4000K
RGAIR-24LED72DMV40	2x4 / 47.75"L x 23.75"W x 3.75"H / 72W 8,265L / Standard .100 Acrylic Prismatic Lens / 4000K

Add "EM" for emergency. Add "SSM" for microwave sensor. Also available in 30K, 35K, & 50K.

### LED Recessed Troffer With Integral Microwave Sensor

Our standard LED troffer with an integral microwave sensor.

ITEM NO.	DESCRIPTION
RG-22LED28DMV40SSM	2x2 / 23.75"L x 23.75"W x 3.75"H / 28W 2,624L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-14LED57DMV40SSM	1x4 / 47.88"L x 12.0"W x 3.75"H / 57W 6,370L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-24LED57DMV40SSM	2x4 / 47.75"L x 23.75"W x 3.75"H / 57W 6,737L / Standard .100 Acrylic Prismatic Lens / 4000K

Add "EM" for emergency. Add "SSM" for microwave sensor. Also available in 30K, 35K, & 50K.



# RECESSED

## LED Recessed Troffer

Our standard troffer has almost unlimited options including 3 different sizes and multiple lens, door, and gasketing options.



ITEM NO.	DESCRIPTION
RG-22LED24DMV40	2x2 / 23.75"L x 23.75"W x 3.75"H / 24W 2,624L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-22LED28DMV40	2x2 / 23.75"L x 23.75"W x 3.75"H / 28W 2,624L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-22LED35DMV40	2x2 / 23.75"L x 23.75"W x 3.75"H / 35W 3,591L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-14LED35DMV40	1x4 / 47.88"L x 12.0"W x 3.75"H / 35W 4,090L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-14LED48DMV40	1x4 / 47.88"L x 12.0"W x 3.75"H / 48W 5,385L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-24LED35DMV40	2x4 / 47.75"L x 23.75"W x 3.75"H / 35W 4,346L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-24LED45DMV40	2x4 / 47.75"L x 23.75"W x 3.75"H / 45W 5,501L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-24LED57DMV40	2x4 / 47.75"L x 23.75"W x 3.75"H / 57W 6,737L / Standard .100 Acrylic Prismatic Lens / 4000K
RG-24LED72DMV40	2x4 / 47.75"L x 23.75"W x 3.75"H / 72W 8,700L / Standard .100 Acrylic Prismatic Lens / 4000K

Add "EM" for emergency. Add "SSM" for microwave sensor. Also available in 30K, 35K, & 50K.

### ITEM NO.

### DESCRIPTION

#### Door & Gasketing Options

(Blank)	Flush Steel Door
FA	Regressed Aluminum Door / White
FAB	Regressed Aluminum Door / Black
G1	Single Gasketed Door / Single (Lens To Door Frame)
G2	Double Gasketed Door / Lens/Frame + Frame To Troffer)
G3	Triple Gasketed Door / (Lens/Frame + Frame/Troffer + Troffer To T-bar Grid)

### ITEM NO.


### DESCRIPTION

#### Lens Options

(Blank)	A12 0.10" Thick Lens
125	A12 0.125" Thick Lens
156	A19 0.156" Thick Lens
CL	Clear 0.10" Thick Lens
CL125	Clear 0.125" Thick Lens
FR	Frosted Lens
SW	Smooth White 0.10" Thick Lens
W5	White Parabolic Louver 0.5"Sq x 0.38"Dp
S5	Specular Parabolic Louver 0.5"Sq x 0.38"Dp
S15	Specular Parabolic Louver 1.5"Sq x 1.0"Dp
S75	Specular Parabolic Louver 0.75"Sq x 0.38"Dp



A125 FR (Blank) Standard



SW S75 S5

1.800.444.9288

mobern.com



# UNDERCABINET



## LED Linkable Undercabinet

An acrylic prismatic lens distributes light evenly while reducing glare and providing visual comfort. Power cord, joiner cable, butt connector, and BX connector included.

ITEM NO.	DESCRIPTION
MLUC-9L5E12040	9"L x 5"W x 1"H / 5W 250L / 4000K
MLUC-12L6E12040	12"L x 5"W x 1"H / 6W 300L / 4000K
MLUC-18L9E12040	18"L x 5"W x 1"H / 9W 450L / 4000K
MLUC-24L11E12040	24"L x 5"W x 1"H / 11W 550L / 4000K
MLUC-33L13E12040	33"L x 5"W x 1"H / 13W 650L / 4000K
MLUC-42L16E12040	42"L x 5"W x 1"H / 16W 900L / 4000K

## Rounded Undercabinet Light

With 5 different sizes, this rounded undercabinet light is perfectly suited for any office, residential, or commercial application you need.

ITEM NO.	DESCRIPTION
MLUCR-12LED7D12030	12.0"L x 2.75"W x 1.0"H / 7W 450L / 3000K
MLUCR-18LED10D12030	18.0"L x 2.75"W x 1.0"H / 10W 675L / 3000K
MLUCR-24LED12D12030	24.0"L x 2.75"W x 1.0"H / 12W 900L / 3000K
MLUCR-36LED18D12030	36.0"L x 2.75"W x 1.0"H / 18W 1,350L / 3000K
MLUCR-48LED23D12030	48.0"L x 2.75"W x 1.0"H / 23W 1,800L / 3000K

Undercabinets come with power cord, joiner cable, butt connector, and a BX connector.

## Dimmable Undercabinet Task Light

This undercabinet features integral LEDs and driver that can be used individually or joined together with a cord, plug, and on/off switch, mini coupler, or 15" joiner cord supplied with every fixture. An optional hardwire junction box is available for hardwire applications.

ITEM NO.	DESCRIPTION
MLEDDUCL-12WH30	12.0"L x 2.0"W x 0.98"H / 5W 250L / White Finish / 3000K
MLEDDUCL-18WH30	17.8"L x 2.0"W x 0.98"H / 8W 389L / White Finish / 3000K
MLEDDUCL-24WH30	24.0"L x 2.0"W x 0.98"H / 11W 525L / White Finish / 3000K
MLEDDUCLJBOX	Junction Box For Hardwire

Fixture comes with mini coupler and 15" joiner cord, 42" cord and plug with integral on/off switch.

## High Lumen LED Tape

Put light exactly where you need it with this high lumen LED tape. Available in warm white, natural, and white.

ITEM NO.	DESCRIPTION
LEDT-5050L24V27	LED High Lumen Tape 1ft Pieces, 4.32W/FT, 180LM/FT, 24v, 27K
LEDT-5050L24V30	LED High Lumen Tape 1ft Pieces, 4.32W/FT, 185LM/FT, 24v, 30K
LEDT-5050L24V40	LED High Lumen Tape 1ft Pieces, 4.32W/FT, 189LM/FT, 24v, 40K
LEDT-CON-HW-10	LED 10 Foot Hardwire Connector
LEDT-EXT-4IN	LED 4 Inch 4 Pin Tape Jumper Cable MtoF
LEDT-EXT-12IN	LED 12 Inch 4 Pin Tape Jumper Cable MtoF
LEDT-EXT-36IN	LED 36 Inch 4 Pin Tape Jumper Cable MtoF
LEDT-CON-MM	LED 4 Pin Tape Male To Male Connector
LEDT-CON-MMT	LED 4 Pin Tape Male To Male T Connector

Priced per foot, 16ft reel. Specify remote driver.

## Remote Driver (Dimmable With Any Standard MLV Triac Leading Edge Control)


ITEM NO.	DESCRIPTION
LEDD-MDCV24V60-120VHW	Magnitude Magnetic Driver 60W 24VDC Encased
LEDD-MDCV24V96-120VHW	Magnitude Magnetic Driver 96W 24VDC Encased
LEDD-MDCV24V150-120VHW	Magnitude Magnetic Driver 150W 24VDC Encased



# Retrofit Kits

Mobern Lighting has the capabilities to meet all of your retrofit needs. Our staff is dedicated to creating a customized lighting experience. Whether you are looking to upgrade your existing fluorescent fixture, replace existing fluorescent tubes with LED tubes, or change to fully integrated LED boards, Mobern Lighting is your one-stop shop.

Before



After



## Economy Center Basket Retrofit

Upgrade your fluorescent troffer to an architectural center basket style LED for better efficiency and aesthetics.

ITEM NO.	DESCRIPTION
RKDISE-22LED24DMVFR40	2x2 / 23.97"L x 23.97"W x 3.65"H / 24W 3,125L / Frosted Lens / 4000K
RKDISE-22LED28DMVFR40	2x2 / 23.97"L x 23.97"W x 3.65"H / 28W 3,610L / Frosted Lens / 4000K
RKDISE-22LED35DMVFR40	2x2 / 23.97"L x 23.97"W x 3.65"H / 35W 4,540L / Frosted Lens / 4000K
RKDISE-24LED32DMVFR40	2x4 / 48.0"L x 23.97"W x 3.65"H / 32W 4,600L / Frosted Lens / 4000K
RKDISE-24LED48DMVFR40	2x4 / 48.0"L x 23.97"W x 3.65"H / 48W 6,890L / Frosted Lens / 4000K
RKDISE-24LED57DMVFR40	2x4 / 48.0"L x 23.97"W x 3.65"H / 57W 7,675L / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, and 50K.

## Center Basket Retrofit

Similar to the RKDISE, this fixture offers the look of a center basket but features an extruded lens and a more curved reflector.

ITEM NO.	DESCRIPTION
RKDIS-22LED24DMVFR40	2x2 / 23.97"L x 23.97"W x 3.65"H / 24W 3,080L / Frosted Lens / 4000K
RKDIS-22LED28DMVFR40	2x2 / 23.97"L x 23.97"W x 3.65"H / 28W 3,360L / Frosted Lens / 4000K
RKDIS-22LED35DMVFR40	2x2 / 23.97"L x 23.97"W x 3.65"H / 35W 4,325L / Frosted Lens / 4000K
RKDIS-24LED32DMVFR40	2x4 / 48.0"L x 23.97"W x 3.65"H / 32W 4,670L / Frosted Lens / 4000K
RKDIS-24LED48DMVFR40	2x4 / 48.0"L x 23.97"W x 3.65"H / 48W 6,780L / Frosted Lens / 4000K
RKDIS-24LED57DMVFR40	2x4 / 48.0"L x 23.97"W x 3.65"H / 57W 7,800L / Frosted Lens / 4000K
RKDIS-24LED62DMVFR40	2x4 / 48.0"L x 23.97"W x 3.65"H / 62W 8,130L / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, and 50K.



**Install in minutes!**  
Place rails between fixture and T-bar on each side. Then latch and secure all-in-one retrofit into place.

# RETROFIT

## Troffer Retrofit Kit

Make your existing troffer LED with this LED retrofit kit that installs easily with just 4 screws.



ITEM NO.	DESCRIPTION
RKT-22LED24DMV40	2x2 / 20.7"L x 20.75"W x 2.38"H / 24W 2,624L / 4000K
RKT-22LED28DMV40	2x2 / 20.7"L x 20.75"W x 2.38"H / 28W 2,979L / 4000K
RKT-22LED35DMV40	2x2 / 20.7"L x 20.75"W x 2.38"H / 35W 3,591L / 4000K
RKT-24LED35DMV40	2x4 / 44.75"L x 20.75"W x 2.38"H / 35W 3,653L / 4000K
RKT-24LED48DMV40	2x4 / 44.75"L x 20.75"W x 2.38"H / 48W 5,088L / 4000K
RKT-24LED57DMV40	2x4 / 44.75"L x 20.75"W x 2.38"H / 57W 6,046L / 4000K
With Integral Sensor	
RKT-22LED28DMV40SS	2x2 / 20.7"L x 20.75"W x 2.38"H / 28W 2,979L / 4000K
RKT-24LED57DMV40SS	2x4 / 44.75"L x 20.75"W x 2.38"H / 57W 6,046L / 4000K

Add "EM" for emergency. Also available in 30K, 35K, and 50K.

## Round Profile Strip Retrofit Kit

This designer retrofit solution with a rounded lens provides a sleek new look as well as an energy saving alternative to T12 or T8 linear strips. Ideal for schools, retail, and warehouses.



ITEM NO.	DESCRIPTION
RKBCR-48LED20DMV40	48.0"L x 4.25"W x 3.9"H / 20W 2,700L / Round Lens / 4000K
RKBCR-48LED30DMV40	48.0"L x 4.25"W x 3.9"H / 30W 3,827L / Round Lens / 4000K
RKBCR-48LED41DMV40	48.0"L x 4.25"W x 3.9"H / 41W 5,103L / Round Lens / 4000K
RKBCR-48LED58DMV40	48.0"L x 4.25"W x 3.9"H / 58W 7,013L / Round Lens / 4000K
RKBCR-96LED40DMV40	96.0"L x 4.25"W x 3.9"H / 40W 4,700L / Round Lens / 4000K
RKBCR-96LED60DMV40	96.0"L x 4.25"W x 3.9"H / 60W 7,654L / Round Lens / 4000K
RKBCR-96LED82DMV40	96.0"L x 4.25"W x 3.9"H / 82W 10,206L / Round Lens / 4000K
RKBCR-96LED116DMV40	96.0"L x 4.25"W x 3.9"H / 116W 14,026L / Round Lens / 4000K

Add "EM" for emergency. Consult to retrofit 5" strip. Also available in 30K, 35K, and 50K.

## Flat Profile Strip Retrofit Kit

The same as our RKBCR fixture above, but with a flat lens for a different look and feel.



ITEM NO.	DESCRIPTION
RKBCF-48LED20DMV40	48.0"L x 4.25"W x 2.78"H / 20W 2,700L / Flat Lens / 4000K
RKBCF-48LED30DMV40	48.0"L x 4.25"W x 2.78"H / 30W 3,500L / Flat Lens / 4000K
RKBCF-48LED41DMV40	48.0"L x 4.25"W x 2.78"H / 41W 4,300L / Flat Lens / 4000K
RKBCF-48LED58DMV40	48.0"L x 4.25"W x 2.78"H / 58W 6,700L / Flat Lens / 4000K
RKBCF-96LED40DMV40	96.0"L x 4.25"W x 2.78"H / 40W 4,700L / Flat Lens / 4000K
RKBCF-96LED60DMV40	96.0"L x 4.25"W x 2.78"H / 60W 6,900L / Flat Lens / 4000K
RKBCF-96LED82DMV40	96.0"L x 4.25"W x 2.78"H / 82W 8,900L / Flat Lens / 4000K
RKBCF-96LED116DMV40	96.0"L x 4.25"W x 2.78"H / 116W 13,400L / Flat Lens / 4000K

Add "EM" for emergency. Consult to retrofit 5" strip. Also available in 30K, 35K, and 50K.



# RETROFIT

## Economy Round Profile Strip Retrofit

This economical, workhorse, strip retrofit provides a versatile solution for many applications including retail, industrial, and mezzanine low-ceiling applications where a wide light distribution is needed.



ITEM NO.	DESCRIPTION
RKFSF-24LED12DMVFR40	24.0"L x 4.25"W x 3.25"H / 12W 1,400L / Frosted Lens / 4000K
RKFSF-48LED24DMVFR40	48.0"L x 4.25"W x 3.25"H / 24W 2,800L / Frosted Lens / 4000K
RKFSF-48LED48DMVFR40	48.0"L x 4.25"W x 3.25"H / 48W 4,800L / Frosted Lens / 4000K
RKFSF-48LED57DMVFR40	48.0"L x 4.25"W x 3.25"H / 57W 5,900L / Frosted Lens / 4000K
RKFSF-96LED62DMVFR40	96.0"L x 4.25"W x 3.25"H / 62W 6,200L / Frosted Lens / 4000K
RKFSF-96LED114DMVFR40	96.0"L x 4.25"W x 3.25"H / 114W 11,700 / Frosted Lens / 4000K

Add "EM" for emergency. Consult to retrofit 5" strip. Also available in 30K, 35K, and 50K.

## LED Strip Ballast Cover Retrofit Kit

This ballast cover kit is easy to install, and provides enhanced output for an existing strip.



ITEM NO.	DESCRIPTION
RKBC-484LED24DMV40	48.0"L x 4.25"W x 0.5"H / 24W 3,470L / 4000K
RKBC-484LED48DMV40	48.0"L x 4.25"W x 0.5"H / 48W 6,555L / 4000K
RKBC-484LED57DMV40	48.0"L x 4.25"W x 0.5"H / 57W 7,915L / 4000K
RKBC-485LED24DMV40	48.0"L x 5.0"W x 0.5"H / 24W 3,470L / 4000K
RKBC-485LED48DMV40	48.0"L x 5.0"W x 0.5"H / 48W 6,555L / 4000K
RKBC-485LED57DMV40	48.0"L x 5.0"W x 0.5"H / 57W 7,915L / 4000K
RKBC-964LED48DMV40	96.0"L x 4.25"W x 0.5"H / 48W 6,940L / 4000K
RKBC-964LED97DMV40	96.0"L x 4.25"W x 0.5"H / 97W 13,118L / 4000K
RKBC-964LED118DMV40	96.0"L x 4.25"W x 0.5"H / 118W 15,832L / 4000K
RKBC-965LED48DMV40	96.0"L x 5.0"W x 0.5"H / 48W 6,940L / 4000K
RKBC-965LED97DMV40	96.0"L x 5.0"W x 0.5"H / 97W 13,118L / 4000K
RKBC-965LED118DMV40	96.0"L x 5.0"W x 0.5"H / 118W 15,832L / 4000K

Add "EM" for emergency. Also available in 30K, 35K, and 50K.

Frosted lens accessory available for 4.25" width to reduce LED brightness. L1085 - 4ft. L1085-TANDEM - 8ft.

## Linear Wall Retrofit

Specially engineered to retrofit perimeter lighting fluorescent systems to a highly efficient LED fixture that will provide even illumination on a wall.



ITEM NO.	DESCRIPTION
RKPWL-436LED19DMVWHFR40	36.0"L x 4.54"W x 5.98"H / 19W 2,250L / White Finish / Frosted Lens / 4000K
RKPWL-448LED25DMVWHFR40	48.0"L x 4.54"W x 5.98"H / 25W 3,000L / White Finish / Frosted Lens / 4000K
RKPWL-496LED50DMVWHFR40	96.0"L x 4.54"W x 5.98"H / 50W 6,000L / White Finish / Frosted Lens / 4000K

Add "EM" for emergency. Also available in 30K, 35K, and 50K.

## CTC/Wall Fixture Retrofit

The RKSEOS features driver-on-board technology and heat sink for excellent light output.



ITEM NO.	DESCRIPTION
RKSEOS-6LED13D12030	EOS Array With 6" Sq Alum Heat Sink / 13W 1,140L / 3000K
RKSEOS-6LED13D12040	EOS Array With 6" Sq Alum Heat Sink / 13W 1,280L / 4000K
RKSEOS-8LED14D12030	EOS Array With 8" Sq Alum Heat Sink / 14W 1,430L / 3000K
RKSEOS-8LED14D12040	EOS Array With 8" Sq Alum Heat Sink / 14W 1,500L / 4000K
RKSEOS-8LED22D12030	EOS Array With 8" Sq Alum Heat Sink / 22W 1,950L / 3000K
RKSEOS-8LED22D12040	EOS Array With 8" Sq Alum Heat Sink / 22W 2,130L / 4000K

# LED CLOSE-TO-CEILING



## Spill Ring Close-To-Ceiling

This stylish ceiling fixture comes in multiple sizes to meet a variety of applications. Matching wall, bath, and linear versions (pages 45 and 64) make this fixture ideal for multi-family or hospitality applications.

ITEM NO.	DESCRIPTION
DECCD-14LED23MVSN40	14.5"Dia x 4.6"H / 23W 2,267L / Satin Nickel Finish / 4000K
DECCD-16LED28MVSN40	16.0"Dia x 4.9"H / 28W 2,600L / Satin Nickel Finish / 4000K
DECCD-18LED35MVSN40	17.8"Dia x 4.9"H / 35W 3,364L / Satin Nickel Finish / 4000K

Consult for other finish options. Consult for emergency and bi-level dimming option. Also available in 30K.



## Drum Fixture

This clean, contemporary look is perfect for kitchens, hallways, laundry rooms, pantries, bathrooms, and general work areas.

ITEM NO.	DESCRIPTION
69-11LED13D12040	11.0"Dia x 3.0"H / 13W 1,000L / 4000K
69-11LED14D12040	11.0"Dia x 3.0"H / 14W 1,400L / 4000K
69-14LED14D12040	13.75"Dia x 3.5"H / 14W 1,400L / 4000K
69-14LED23D12040	13.75"Dia x 3.5"H / 23W 1,900L / 4000K

Add "OS" for occupancy sensor. Also available in 30K.



## Mushroom Fixture

This fixture features a circular "puff" diffuser suitable for closets, laundry areas, and pantries in commercial or residential applications.

ITEM NO.	DESCRIPTION
68-11LED12D12040	11.0"Dia x 3.0"H / 12W 800L / 4000K
68-11LED15D12040	11.0"Dia x 3.0"H / 15W 1,200L / 4000K
68-14LED15D12040	13.75"Dia x 3.5"H / 15W 1,200L / 4000K
68-14LED22D12040	13.75"Dia x 3.5"H / 22W 1,800L / 4000K

Add "OS" for occupancy sensor. Also available in 30K.



## Dome Fixture

This clean stylized dome is suitable for a wide variety of residential and commercial lighting applications.

ITEM NO.	DESCRIPTION
DECCE-11LED13D12040	10.88"Dia x 3.88"H / 13W 1,280L / 4000K
DECCE-11LED14D12040	10.88"Dia x 3.88"H / 14W 1,500L / 4000K
DECCE-14LED14D12040	14.0"Dia x 4.25"H / 14W 1,500L / 4000K
DECCE-14LED22D12040	14.0"Dia x 4.25"H / 22W 2,130L / 4000K

Also available in 30K.



## Ultra Thin Faux Downlight (Wet Location)

Featuring a special regressed lens, these faux downlights provide even, comfortable illumination. These edge lit fixtures can be used indoor and outdoor and come in a round or square silhouette.

ITEM NO.	DESCRIPTION
CTCS-5LED10D120WH30	6.28"L x 6.28"W x 0.63"H / 10W 660L / White Finish / 3000K
CTCS-5LED10D120BN30	6.28"L x 6.28"W x 0.63"H / 10W 660L / Brushed Nickel Finish / 3000K
CTCS-7LED15D120WH30	8.0"L x 8.0"W x 0.63"H / 15W 1,000L / White Finish / 3000K
CTCS-7LED15D120BN30	8.0"L x 8.0"W x 0.63"H / 15W 1,000L / Brushed Nickel Finish / 3000K
CTCR-5LED10D120WH30	5.5"Dia x 0.63"H / 10W 660L / White Finish / 3000K
CTCR-5LED10D120BN30	5.5"Dia x 0.63"H / 10W 660L / Brushed Nickel Finish / 3000K
CTCR-7LED15D120WH30	7.0"Dia x 0.63"H / 15W 1,000L / White Finish / 3000K
CTCR-7LED15D120BN30	7.0"Dia x 0.63"H / 15W 1,000L / Brushed Nickel Finish / 3000K



# LED CLOSE-TO-CEILING

## Micro Economy LED Surface Mount (Wet Location)

This low profile disc mounts directly to the junction box or to 4" or 6" recessed housing to provide a uniform look. This fixture is also suitable for wet locations.



ITEM NO.	DESCRIPTION
CTCE-6LED15WH30	7.4"Dia x 1.26"H / 15W 1,000L / White Finish / 3000K
CTCE-6LED15BN30	7.4"Dia x 1.26"H / 15W 1,000L / Brushed Nickel Finish / 3000K
CTCE-6RECACC	Recessed Accessory Kit to Retrofit CTCE Series into 6" Recessed White Can Housings



Shown with pull switch.

## Stylish Economical LED Surface Mount

This popular low profile disc is now available with a pull switch for those applications that require an integral on/off switch. It is especially useful in closet or storage areas.

ITEM NO.	DESCRIPTION
MTDL6-LED15D120WH40	7.38"Dia x 1.5"H / 15W 1,100L / White Finish / 3000K
MTDL6-LED15D120BA40	7.38"Dia x 1.5"H / 15W 1,100L / Brushed Aluminum Finish / 3000K
MTDL6-LED15D120BZ40	7.38"Dia x 1.5"H / 15W 1,100L / Bronze Finish / 3000K
MTDL6RECACC	Recessed Accessory Kit for MTDL

Add "PS" for pull switch.


## Tapered Disc Luminaire With Occupancy Sensor

This disc light incorporates an integral motion sensor with a 15 foot range from an 8 foot ceiling to conserve energy when the area is not occupied.



ITEM NO.	DESCRIPTION
MTDLOS-8LED15D120WHFR30	7.87"Dia x 1.42"H / 15W 1,100L / White Finish / Frosted Lens / 3000K

## New Product!



# LED CLOSE-TO-CEILING

## Micro LED Surface Mount (Wet Location)

This low profile disc mounts directly to the junction box or to 4" or 6" recessed housing to provide a uniform look. This fixture is also suitable for wet locations.



ITEM NO.	DESCRIPTION
CTCM-4LED12D120WH30	5.9"Dia x 1.2"H / 12W 876L / White Finish / 3000K
CTCM-6LED15D120WH30	7.4"Dia x 1.2"H / 15W 1,095L / White Finish / 3000K
CTCM-9LED26D120WH30	9.5"Dia x 1.4"H / 26W 1,700L / White Finish / 3000K
CTCM4REACC	Recessed Accessory Kit to Retro CTCM4 Series into 4" Recessed White Can Housings
CTCM6REACC	Recessed Accessory Kit to Retro CTCM6 Series into 6" Recessed White Can Housings
CTCM-11LED28D120BN30	11.5"Dia x 1.4"H / 28W 1,700L / Brushed Nickel Finish / 3000K
CTCM-11LED28D120WH30	11.5"Dia x 1.4"H / 28W 1,700L / White Finish / 3000K
CTCM-15LED40D120BN30	15.5"Dia x 1.4"H / 40W 2,500L / Brushed Nickel Finish / 3000K
CTCM-15LED40D120WH30	15.5"Dia x 1.4"H / 40W 2,500L / White Finish / 3000K

Consult for other finish options.



## Micro LED Surface Mount With 277V Or Emergency (Wet Location)

This emergency disc for low plenum locations is an affordable solution to hiding emergency fixtures. It includes a specially designed junction box for installation before drywall. Suitable for wet locations.

ITEM NO.	DESCRIPTION
CTCM-6LED15277WH30	7.4"Dia x 1.2"H / 15W 2,020L / White Finish / 3000K
CTCM-6LED15D120WH30EM	7.4"Dia x 1.2"H / 15W 1,095L / White Finish / 3000K / Emergency Battery Backup



## Spill Ring Wall Bracket

This wall bracket is ideal for corridors and entries. Matching wall, bath, and linear versions (pages 45 and 62) make this fixture ideal for multifamily or hospitality applications.

ITEM NO.	DESCRIPTION
DECWD-LED14120SN30	10.5"L x 9.4"W x 4.0"Dia / 14W 950L / Satin Nickel Finish / 3000K
DECWD-LED22MVSN30	10.5"L x 9.4"W x 4.0"Dia / 22W 1,900L / Satin Nickel Finish / 3000K

Change "SN" to "BZ" for oil rubbed bronze finish. Consult for GU base. Consult for other color temperature options.



## Cuff Link Wall Bracket

A curved bent glass diffuser held by satin nickel or oil rubbed bronze hardware provides comfortable lighting for corridors and circulation spaces. Open top and bottom does not collect debris.

ITEM NO.	DESCRIPTION
DECWF-LED16120SN30	11.5"L x 10.3"W x 4.0"Dia / 16W 1,027L / Satin Nickel Finish / 3000K

Change "SN" to "BZ" for oil rubbed bronze finish. Consult for GU base. Consult for other color temperature options.



## Wall Bracket

This wall sconce with a closed top and bottom are ideal for locations wanting to minimize cleaning issues.

ITEM NO.	DESCRIPTION
DECWV-LED15120SNFR30	10.0"L x 7.2"W x 4.0"Dia / 15W 1,150L / Satin Nickel Finish / Frosted Lens / 3000K

Change "SN" to "BZ" for oil rubbed bronze finish. Consult for GU base. Consult for other color temperature options.



# ENCLOSURES



Acrylic Lens Options		2ft	4ft	8ft
<b>RF</b>	Ribbed Frosted	✓*	✓*	✓*
<b>RC</b>	Ribbed Clear	✓*	✓*	✓*
<b>SSC</b>	Shallow Smooth Clear		✓*	
<b>SSF</b>	Shallow Smooth Frosted		✓*	
<b>SC</b>	Smooth Clear	✓*	✓*	✓*
<b>SF</b>	Smooth Frosted	✓*	✓*	✓*

\*Add "P" in front of lens options above for Polycarbonate lens at additional cost.



## Enclosures Low Bay (Wet Location)

This engineered lighting system is designed for exterior applications where weatherproof lighting is required. A tough diffuser resists breakage while providing excellent lighting.

ITEM NO.	DESCRIPTION
VW-2LED24DMVSF40	26.6"L x 7.3"W / 24W 2,700L / Smooth Frosted Lens / 4000K
VW-2LED28DMVSF40	26.6"L x 7.3"W / 28W 3,300L / Smooth Frosted Lens / 4000K
VW-4LED48DMVSSF40	51.8"L x 7.3"W / 48W 5,570L / Smooth Frosted Lens / 4000K
VW-4LED57DMVSSF40	51.8"L x 7.3"W / 57W 6,790L / Smooth Frosted Lens / 4000K
VW-8LED97DMVSF40	100.0"L x 7.3"W / 97W 11,140L / Smooth Frosted Lens / 4000K
VW-8LED114DMVSF40	100.0"L x 7.3"W / 114W 13,580L / Smooth Frosted Lens / 4000K

For Emergency, add EM. Consult for sensors and stainless steel latches. Also available in 30K, 35K, & 50K.

## Enclosures Parking Garage (Wet Location)


A wider distribution version of the above fixture.

ITEM NO.	DESCRIPTION
VW-4LED48DMVWDRF40	51.8"L x 7.3"W / 48W 5,570L / Ribbed Frosted Lens / 4000K
VW-4LED57DMVWDRF40	51.8"L x 7.3"W / 57W 6,790L / Ribbed Frosted Lens / 4000K
VW-4LED72DMVWDRF40	51.8"L x 7.3"W / 72W 7,000L / Ribbed Frosted Lens / 4000K
VW-8LED97DMVWDRF40	98.5"L x 7.3"W / 97W 11,140L / Ribbed Frosted Lens / 4000K
VW-8LED114DMVWDRF40	98.5"L x 7.3"W / 114W 13,580L / Ribbed Frosted Lens / 4000K

For emergency, add EM. Consult for sensors and stainless steel latches. Also available in 30K, 35K, 50K.


## Clips and Hangers Accessories:

Replacement White Latch (sold individually)



► **H123** - 2ft., 4ft., 8ft.\*

Stainless Steel Latch Kit Set



► **H126** - 2ft. & 4ft.  
► **H127** - 8ft.

Stainless Steel Mounting Bracket 45°



► **VW-MB2L-2PK-45DEG**  
Mounts fixture at 45° angle from wall or ceiling

Stainless Steel Mounting Bracket w/ Bail



► **VW-MB2L-B-2PK**  
(Recommended for cable hanging)

Stainless Steel Mounting Bracket



► **VW-MB2L-2PK**

\*To replace latches on entire fixture order 6 latches for 2ft., 8 latches for 4ft., and 14 latches for 8ft.

# ENCLOSURES



Deep lens not available for VWN4.



## Narrow LED Vaportight

A narrow 4.4" wide version of our enclosures is great for parking garages, poultry farms, car washes, marinas, and other applications susceptible to corrosive and wet conditions.

ITEM NO.	DESCRIPTION
VWN-4LED48DMVRF40	51.8"L x 4.4"W / 48W 5,600L / Ribbed Frosted Lens / 4000K

Also available in 30K, 35K, & 50K.



Standard 3/4" hub allows standard electrical accessories for installation.

## Outdoor Sign Lighter with 3/4" Hub (Wet Location)

This 360° rotating sign lighter is great for parking and commercial retail outdoor areas for sign and walkway lighting.

ITEM NO.	DESCRIPTION
AOD-48LED48DMV40	54.5"L x 5.25"W x 3.06"H / 48W 4,800L / Aluminum Extrusion with Clear Lens / 4000K
AOD-48LED57DMV40	54.5"L x 5.25"W x 3.06"H / 57W 5,700L / Aluminum Extrusion with Clear Lens / 4000K
AOD-96LED96DMV40	102.5"L x 5.25"W x 3.06"H / 48W 4,800L / Aluminum Extrusion with Clear Lens / 4000K
AOD-96LED114DMV40	102.5"L x 5.25"W x 3.06"H / 114W 11,400L / Aluminum Extrusion with Clear Lens / 4000K

Also available in 30K, 35K, & 50K.


## Outdoor Sign Lighter

This outdoor sign lighter comes in 3 different sizes with multiple distribution options, and its low profile design keeps the fixture placement discrete for both ground and wall mounted applications.

ITEM NO.	DESCRIPTION
SLT-24LED41DMVBKT341	24.0"L x 3.8"W x 5.77"H / 41W 3,908L / Black Finish / Type III Distribution / 4100K
SLT-36LED81DMVBKT341	36.0"L x 3.8"W x 5.77"H / 81W 7,816L / Black Finish / Type III Distribution / 4100K
SLT-48LED122DMVBKT341	48.1"L x 3.8"W x 5.77"H / 122W 11,724L / Black Finish / Type III Distribution / 4100K
SLT-48LED122DMVBKT541	24.0"L x 3.8"W x 5.77"H / 41W 3,978L / Black Finish / Type V Wide Distribution / 4100K
SLT-48LED122DMVBKT541	36.0"L x 3.8"W x 5.77"H / 81W 7,956L / Black Finish / Type V Wide Distribution / 4100K
SLT-48WLED122DMVBKT541	48.1"L x 3.8"W x 5.77"H / Type V Wide Distribution / 122W 11,934L / Black Finish / 4100K

Also available in 50K.

## Enclosed & Gasketed Fixture



Our new profile series is ideal for low bay area lighting where wet rated enclosures are required. Co-extruded 5VA plastic housing and lens ensure a fully encapsulated enclosure, and can be used for wash down and where chemicals are present.

ITEM NO.	DESCRIPTION
PRF-12LED24DMVAGY40	2'L x 3.86"W x 3.75"H / 24W / Acrylic Housing / Gray Finish / 4000K
PRF-14LED48DMVAGY40	4'L x 3.86"W x 3.75"H / 48W / Acrylic Housing / Gray Finish / 4000K
PRF-18LED96DMVAGY40	8'L x 3.86"W x 3.75"H / 96W / Acrylic Housing / Gray Finish / 4000K

Change "GY" to "WH" for white finish. Also available in 30K, 35K, & 50K

## Linear Vandal Resistant

Ideal for high-abuse areas such as parking garages and school corridors.

ITEM NO.	DESCRIPTION
SVP-48LED48DMV50	50.25"L x 8.25"W x 4.5"H / 48W 5,570L / 5000K
SVP-48LED72DMV50	50.25"L x 8.25"W x 4.5"H / 72W 7,200L / 5000K

Also available in 30, 35, & 40K

# Outdoor Lighting

Mobern offers a comprehensive selection of LED fixtures to meet all of your exterior applications from site lighting to decorative outdoor wall fixtures. Our wall packs, flood lights, and wide area lighting fixtures are designed to meet today's demanding specifications in a range of lumen outputs and energy requirements including dark sky codes and maintenance targets. All of the exterior fixtures are focused on delivering safety, security, and sustainability at a reasonable price.



## Square Canopy (Wet Location)

With wide distribution, this canopy is perfect for parking structures, storage areas, shopping area walkways, and low level security.



ITEM NO.	DESCRIPTION
CPYSA-10LED27DMVBZ50	9.52"L x 9.52"W x 3.19"H / 27W 3,800L / Bronze Finish / 5000K
CPYSA-10LED40DMVBZ50	9.52"L x 9.52"W x 3.19"H / 40W 5,450L / Bronze Finish / 5000K
CPYSA-10LED60DMVBZ50	9.52"L x 9.52"W x 3.19"H / 60W 8,000L / Bronze Finish / 5000K

Add "EM" for emergency. Add "OS" for occupancy sensor. Consult for other color temperatures.

## Round Canopy (Wet Location)

Our classic wide distribution round canopy is suited for shopping areas, walkways, parking garages, storage areas, and low level security.



ITEM NO.	DESCRIPTION
CPYRA-12LED30DMVWH50	12.0"Dia x 3.32"H / 30W 3,800L / White Finish / 5000K
CPYRA-12LED45DMVWH50	12.0"Dia x 3.32"H / 45W 5,500L / White Finish / 5000K
CPYRA-12LED60DMVWH50	12.0"Dia x 3.32"H / 60W 7,600L / White Finish / 5000K

Add "EM" for emergency. Add "OS" for occupancy sensor. Consult for other color temperatures.



# OUTDOOR



## Outdoor Wet Location Wall/Ceiling (Bug Proof)



Maintenance-free, bug proof, and wet location rated this fixture is great for almost any outdoor application.

ITEM NO.	DESCRIPTION
GLO-12LED15D120BK40	11.81"Dia x 3.61"H / Open Frame / 15W 1,350L / Black Finish / 4000K
GLO-12LED15D120BK30	11.81"Dia x 3.61"H / Open Frame / 15W 1,350L / Black Finish / 3000K
GLO-12LED15D120WH40	11.81"Dia x 3.61"H / Open Frame / 15W 1,350L / White Finish / 4000K
GLO-12LED15D120WH30	11.81"Dia x 3.61"H / Open Frame / 15W 1,350L / White Finish / 3000K

Add "E" after "GLO" for eyelid version. Add "OS" for occupancy sensor.



## Die Cast Round Bulkheads (Wet Location)



These round bulkheads are designed to replace HID lighting systems up to 100W MH or HPS. Typical applications include public buildings, condominiums, schools, and hospitality.

ITEM NO.	DESCRIPTION
ERBO-LED20DMVBZ50	12.5"Dia x 3.94"H / Open Frame / 20W 2,230L / Bronze Finish / 5000K
ERBG-LED20DMVBZ50	12.5"Dia x 4.38"H / Grid Frame / 20W 1,897L / Bronze Finish / 5000K
ERBE-LED20DMVBZ50	12.5"Dia x 4.38"H / Eyelid Frame / 20W 1,858L / Bronze Finish / 5000K

Add "EM" for emergency. Add "PC120" or "PC277" for photocell. Add "SSM" for internal microwave sensor. Change "BZ" to "WH" for white finish. Also available in 30K & 40K.



## Die Cast Square Bulkheads (Wet Location)



These square bulkheads are designed to replace HID lighting systems up to 100W MH or HPS. Typical applications include public buildings, condominiums, schools, and hospitality.

ITEM NO.	DESCRIPTION
ESBO-LED20DMVBZ50	12.5"L x 12.5"W x 4.94"H / Open Frame / 20W 1,477L / Bronze Finish / 5000K
ESBG-LED20DMVBZ50	12.5"L x 12.5"W x 4.94"H / Grid Frame / 20W 1,846L / Bronze Finish / 5000K
ESBE-LED20DMVBZ50	12.5"L x 12.5"W x 4.94"H / Eyelid Frame / 20W 1,436L / Bronze Finish / 5000K

Add "EM" for emergency. Add "PC120" or "PC277" for photocell. Add "SSM" for internal microwave sensor. Change "BZ" to "WH" for white finish. Also available in 30K & 40K.



## Wall Cylinders (Turtle Friendly)

For sensitive outdoor applications, these turtle and dark sky friendly wall cylinders are a perfect choice.

ITEM NO.	DESCRIPTION
MWCD-12INCLEDDWH40	5.0"Dia x 12.0"H x 7.75"Dp / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish
MWCD-8INCLEDDWH40	5.0"Dia x 7.25"H x 7.75"Dp / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish

Change "WH" to "BK" for black finish.



# OUTDOOR



## Close-To-Ceiling (Wet Location)

Available in round or square housing and black or white finish, this fixture is commonly used in entryways, residential exteriors, stairways, walkways, parking garages, and storage areas.

ITEM NO.	DESCRIPTION
WRC-INCLEDDWHWH40	9.38"Dia x 4.5"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Lens
WRC-LED23D120WHWH40	9.38"Dia x 4.5"H / 23W 1,900L / White Finish / White Lens / 4000K
WRC-LED22MVWHWH40	9.38"Dia x 4.5"H / 22W 1,824L / White Finish / White Lens / 4000K
WSC-INCLEDDWHWH40	10.0"L x 10.0"W x 4.5"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Lens
WSC-LED23D120WHWH40	10.0"L x 10.0"W x 4.5"H / 23W 1,900L / White Finish / White Lens / 4000K
WSC-LED22MVWHWH40	10.0"L x 10.0"W x 4.5"H / 22W 1,824L / White Finish / White Lens / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.



## Outdoor Octagon Series

Where you need a more stylized picture, choose this durable, damp location fixture molded of non-corrosive and UV-resistant resins.

ITEM NO.	DESCRIPTION
MOCL-10INCLEDDWH40	10.25"Dia x 5.75"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish
MOCL-10LED14D120WH40	10.25"Dia x 5.75"H / 14W 1,400L / White Finish / 4000K
MOCL-10LED23D120WH40	10.25"Dia x 5.75"H / 23W 1,900L / White Finish / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.



## Vapor Proof (Wet Location)

Built for harsh environments, these keep moisture, dust, and dirt from entering the fixture. Ideal applications include: industrial parks, public transit, airports, and medical facilities.



ITEM NO.	DESCRIPTION
VPL-GGCM14W50KV8SB	5.56"W x 11.04"H / Ceiling Mount / 14W 900L / Silver Finish / 5000K
VPL-GGWM14W50KV8SB	11.38"H x 7.35"Dp / Wall Mount / 14W 900L / Silver Finish / 5000K



## Wall Cylinder



These wall mounted cylinders provide a choice of narrow, medium, or wide distribution, and are designed to replace HID lighting systems. They are available in uplight or downlight only as well as both up and down light.

ITEM NO.	DESCRIPTION
MWCTRS-BLED20DMVBZ41	5.75"Dia x 10.25"H x 8.86"Dp / 100° Reflector / 20W 2,313L / Bronze Finish / 4100K
MWCTRD-BLED1U1D40DMVBZ41	5.75"Dia x 12.5"H x 8.86"Dp / 100° Reflector / 40W 2,173L Up 2,173L Down / Bronze Finish / 4100K

Add "EM" for emergency. Change "BZ" to "BK" for black finish.

# OUTDOOR



## Vandal Proof Square

This utilitarian workhorse is ideal for circulation spaces in commercial or multifamily applications. Consult factory for tamper-proof and other lens options.

ITEM NO.	DESCRIPTION
SVP10-INCLEDDWH40	10.5"L x 10.5"W x 4.5"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish
SVP10-LED14D120WH40	10.5"L x 10.5"W x 4.5"H / 14W 1,400L / White Finish / 4000K
SVP10-LED23D120WH40	10.5"L x 10.5"W x 4.5"H / 23W 1,900L / White Finish / 4000K



## Square Ceiling LED

This traditionally designed porch light is commercial grade and suitable for wet locations.

ITEM NO.	DESCRIPTION
MCBP-INCLEDDWHFR40	8.25"L x 8.25"W x 4.75"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MCBP-LED13D120WHFR40	8.25"L x 8.25"W x 4.75"H / 13W 1,000L / White Finish / Frosted Lens / 4000K
MCBP-LED11MVWHFR40	8.25"L x 8.25"W x 4.75"H / 14W 1,400L / White Finish / Frosted Lens / 4000K
MBBP-INCLEDDWHFR40	10.25"L x 10.25"W x 5.5"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MBBP-LED23D120WHFR40	10.25"L x 10.25"W x 5.5"H / 23W 1,900L / White Finish / Frosted Lens / 4000K
MBBP-LED22MVWHFR40	10.25"L x 10.25"W x 5.5"H / 22W 1,800L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.



## Ceiling Globes

Classic globe and jar style fixtures suitable for outdoor applications.

ITEM NO.	DESCRIPTION
MSN-CCINCLEDDWHGCP40	6"Dia x 8"H / Cylinder Ceiling Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Globe
MSN-CTINCLEDDWHGW40	6"Dia x 8"H / Tapered Ceiling Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Globe

Change "WH" to "BK" for black finish. Also available in 30K.



## Cylindrical Jars

Classic globe and jar style fixtures suitable for outdoor applications.

ITEM NO.	DESCRIPTION
MSN-CCINCLEDDWHRWH40	4.25"Dia x 8.5"H / Cylinder Ceiling Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Rounded Jar
MSN-CTINCWHRCP	4.25"Dia x 8.5"H / Tapered Ceiling Mount / Incandescent Socket / White Finish / Clear Prismatic Rounded Jar
MSN-CTINCLEDDWHJWH40	4.38"Dia x 9.88"H / Tapered Ceiling Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Jar

Change "WH" to "BK" for black finish. Also available in 30K.



## Utility LED

This utilitarian wall mount is ideal for circulation spaces in commercial or multifamily applications.

ITEM NO.	DESCRIPTION
WSPC-INCLEDD40	7.75"H x 5.25"Dp / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included
WSPC-LED13D12040	7.75"H x 5.25"Dp / 13W 1,000L / 4000K
WMPC-INCLEDD40	10.5"H x 6.0"Dp / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included
WMPC-LED13D12040	10.5"H x 6.0"Dp / 13W 1,000L / 4000K
WLPLC-ED15DMVCA40	13.0"L x 4.0"W x 5.0"H / 15W 1,500L / Clear Acrylic Lens / 4000K

Consult for other color temperatures and lens options.



# OUTDOOR



MCEO



MCEOG



MCEOC



MCEOS



MCER



MCERG



MCERC

## Nautical Oval Wall Or Ceiling

This oval commercial-grade wall or ceiling mounted fixture is suitable for wet locations.

ITEM NO.	DESCRIPTION
MCEO-INCLEDDWHFR40	10.63"L x 6.0"W x 4.25"H / Open Frame / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MCEO-LED13D120WHFR40	10.63"L x 6.0"W x 4.25"H / Open Frame / 13W 1,000L / White Finish / Frosted Lens / 4000K
MCEO-LED11MVWHFR40	10.63"L x 6.0"W x 4.25"H / Open Frame / 11W 912L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.

ITEM NO.	DESCRIPTION
MCEOG-INCLEDDWHFR40	10.63"L x 6.0"W x 4.5"H / Grill Frame / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MCEOG-13D120WHFR40	10.63"L x 6.0"W x 4.5"H / Grill Frame / 13W 1,000L / White Finish / Frosted Lens / 4000K
MCEOG-11MVWHFR40	10.63"L x 6.0"W x 4.5"H / Grill Frame / 11W 912L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.

ITEM NO.	DESCRIPTION
MCEOS-INCLEDDWHFR40	10.63"L x 6.0"W x 4.5"H / Hood Frame / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MCEOS-LED13D120WHFR40	10.63"L x 6.0"W x 4.5"H / Hood Frame / 13W 1,000L / White Finish / Frosted Lens / 4000K
MCEOS-LED11MVWHFR40	10.63"L x 6.0"W x 4.5"H / Hood Frame / 11W 912L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.

## Nautical Round Wall Or Ceiling

This round commercial-grade wall or ceiling mounted fixture is suitable for wet locations.

ITEM NO.	DESCRIPTION
MCER-INCLEDDWHFR40	10.38"Dia x 5.25"H / Open Frame / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MCER-LED23D120WHFR40	10.38"Dia x 5.25"H / Open Frame / 23W 1,900L / White Finish / Frosted Lens / 4000K
MCER-LED22MVWHFR40	10.38"Dia x 5.25"H / Open Frame / 22W 1,824L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.


ITEM NO.	DESCRIPTION
MCERG-INCLEDDWHFR40	10.38"Dia x 5.38"H / Grill Frame / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MCERG-LED23D120WHFR40	10.38"Dia x 5.38"H / Grill Frame / 23W 1,900L / White Finish / Frosted Lens / 4000K
MCERG-LED22MVWHFR40	10.38"Dia x 5.38"H / Grill Frame / 22W 1,824L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.

ITEM NO.	DESCRIPTION
MCERC-INCLEDDWHFR40	10.38"Dia x 5.25"H / Grid Frame / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MCERC-LED23D120WHFR40	10.38"Dia x 5.25"H / Grid Frame / 23W 1,900L / White Finish / Frosted Lens / 4000K
MCERC-LED22MVWHFR40	10.38"Dia x 5.25"H / Grid Frame / 22W 1,824L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Also available in 30K.

# OUTDOOR



## Nautical Lanterns & Post Tops

These nautically styled fixtures are molded of durable non-corrosive UV resistant resins and are suitable for wet locations.

ITEM NO.	DESCRIPTION
MNO-BINCLEDDWH40	10.06"W x 10.0"H / Bollard Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish

MNO-BLED13D120WH40	10.06"W x 10.0"H / Bollard Post Top / 13W 1,000L / White Finish / 4000K
--------------------	---

Change "WH" to "BK" for black finish. Also available in 30K.

ITEM NO.	DESCRIPTION
MNO-P2INCLEDWHCP40	23.38"W x 13.0"H / Double Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Lens

MNO-P2LED26D120WHCP40	23.38"W x 13.0"H / Double Post Top / 26W 2,000L / White Finish / Clear Prismatic Lens / 4000K
-----------------------	---

MNO-P2LED22MVWHWH40	23.38"W x 13.0"H / Double Post Top / 22W 1,824L / White Finish / White Lens / 4000K
---------------------	---

MNO-PINCLEDWHCP40	15"W x 13"H / Single Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Lens
-------------------	---

MNO-PLED13D120WHCP40	15"W x 13"H / Single Post Top / 13W 1,000L / White Finish / Clear Prismatic Lens / 4000K
----------------------	--

MNO-PLED11MVWHWH40	15"W x 13"H / Single Post Top / 11W 912L / White Finish / White Lens / 4000K
--------------------	--

Change "WH" to "BK" for black finish. Add "PC" for photocell (not available on MNOB). Also available in 30K.

ITEM NO.	DESCRIPTION
MNO-WINCLEDWHCP40	13"H x 11"Dp / Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Lens

MNO-WLED13D120WHCP40	13"H x 11"Dp / Wall Mount / 13W 1,000L / White Finish / Clear Prismatic Lens / 4000K
----------------------	--

MNO-WLED11MVWHWH40	13"H x 11"Dp / Wall Mount / 11W 912L / White Finish / White Lens / 4000K
--------------------	--

Change "WH" to "BK" for black finish. Add "PC" for photocell (not available on MNOB). Also available in 30K.

## Globe Lanterns & Post Tops

These classic globe lanterns & post tops are molded of durable non-corrosive UV resistant resins and are suitable for wet locations. Post tops fit most 3" diameter posts.

ITEM NO.	DESCRIPTION
MGO-L8INCLEDWHCP40	8.0"Dia x 15.5"H / Long Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Lens

MGO-P10INCLEDWHCP40	10.0"Dia x 12.75"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Lens
---------------------	--

MNG-P12INCLEDWHCP40	12"Dia x 12"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Lens
---------------------	---

MNG-P14INCLEDWHCP40	14"Dia x 14"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Lens
---------------------	---

MNG-P16INCLEDWHCP40	16"Dia x 16"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Prismatic Lens
---------------------	---

Change "WH" to "BK" for black finish. Also available in 30K.

## LED A19/E26 Lamp



- ▶ 9.5 Watts
- ▶ 800 Lumens 120V 3000K or 4000K
- ▶ Replaces 60W incandescent or 13W CFL
- ▶ 30 = CRI 80 / 40 = CRI 90
- ▶ 15,000 hour life
- ▶ Triac dimmable
- ▶ 3 year warranty



# OUTDOOR



## Hutton Lanterns & Post Tops

Square style fade and rust resistant composite construction lanterns & post tops suitable for wet locations. Post tops fit most 3" diameter posts.

ITEM NO.	DESCRIPTION
MHUT-LINCLEDWHCL40	6.4"W x 8.5"Dp x 14.4"H / Large Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHUT-LLED13D120WHCL40	6.4"W x 8.5"Dp x 14.4"H / Large Wall Mount / 13W 1,280L / White Finish / Clear Lens / 4000K
MHUT-WINCLEDWHCL40	5.0"W x 6.8"Dp x 11.6"H / Small Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHUT-WLED13D120WHCL40	5.0"W x 6.8"Dp x 11.6"H / Small Wall Mount / 13W 1,280L / White Finish / Clear Lens / 4000K
MHUT-PINCLEDWHCL40	6.35"L x 6.35"W x 15.0"H / Small Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHUTP-LED13D120WHCL40	6.35"L x 6.35"W x 15.0"H / Small Wall Mount / 13W 1,280L / White Finish / Clear Lens / 4000K

Change "WH" to "BK" or "BZ" for black or bronze finish. Change "CL" to "FR" for frosted lens. Add "PC" for photocell (wall mount only). Also available in 30K.

## Horizon Lanterns & Post Tops

Modern style fade and rust resistant composite construction lanterns & post tops suitable for wet locations. Post tops fit most 3" diameter posts.

ITEM NO.	DESCRIPTION
MHZ-W9INCLEDWHCL40	9.0"Dia x 10.5"Dp x 12.2"H / Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHZ-W9-LED13D120WHCL40	9.0"Dia x 10.5"Dp x 12.2"H / Wall Mount / 13W 1,280L / White Finish / Clear Lens / 4000K
MHZ-P9INCLEDWHCL40	9"Dia x 14"H / Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHZ-P9LED13D120WHCL40	9"Dia x 14"H / Wall Mount / 13W 1,280L / White Finish / Clear Lens / 4000K

Change "WH" to "BK" or "BZ" for black or bronze finish. Change "CL" to "FR" for frosted lens. Add "PC" for photocell (wall mount only). Also available in 30K.

## Highland Lanterns & Post Tops

Sleek style fade and rust resistant composite construction lanterns & post tops suitable for wet locations. Post tops fit most 3" diameter posts.

ITEM NO.	DESCRIPTION
MHI-LINCLEDWHCL40	7.4"Dia x 9.0"Dp x 15.25"H / Large Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHI-LLED13D120WHCL40	7.4"Dia x 9.0"Dp x 15.25"H / Large Wall Mount / 13W 1,280L / White Finish / Clear Lens / 4000K
MHI-WINCLEDWHCL40	5.75"Dia x 7.1"Dp x 12.75"H / Small Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHI-WLED13D120WHCL40	5.75"Dia x 7.1"Dp x 12.75"H / Small Wall Mount / 13W 1,280L / White Finish / Clear Lens / 4000K
MHI-PINCLEDWHCL40	7.25"Dia x 17.25"H / Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHI-PLED13D120WHCL40	7.25"Dia x 17.25"H / Post Top / 13W 1,280L / White Finish / Clear Lens / 4000K

Change "WH" to "BK" or "BZ" for black or bronze finish. Change "CL" to "FR" for frosted lens. Add "PC" for photocell (wall mount only). Also available in 30K.



# OUTDOOR

## Bradford Laterns & Post Tops

Short and long tail lanterns & post tops suitable for outdoor applications in residential and commercial areas.



ITEM NO.	DESCRIPTION
MBR-LINCLEDWHFR40	21"H x 8"Dp / Long Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MBRL-LED13D120WHFR40	21"H x 8"Dp / Long Tail Wall Mount / 13W 1,000L / White Finish / Frosted Lens / 4000K
MBR-PINCLEDWHFR40	8"L x 8"W x 15"H / Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MBR-PLED13D120WHFR40	8"L x 8"W x 15"H / Post Top / 13W 1,000L / White Finish / Frosted Lens / 4000K
MBR-WINCLEDWHFR40	15"H x 8"Dp / Short Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MBR-WLED13D120WHFR40	15"H x 8"Dp / Short Tail Wall Mount / 13W 1,000L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Change "FR" to "CL" or "WH" for clear or white lens. Add "PC" for photocell (not available on post top). Also available in 30K.

## Colonial Laterns & Post Tops

Short and long tail lanterns & post tops suitable for outdoor applications in residential and commercial areas.



ITEM NO.	DESCRIPTION
MCO-LINCWHCF	8.0"W x 17.5"H / Long Tail Wall Mount / Incandescent Socket / White Finish / Clear Flemish Lens
MCO-LLED13D120WHCF40	8.0"W x 17.5"H / Long Tail Wall Mount / 13W 1,000L / White Finish / Clear Flemish Lens / 4000K
MCO-PLED13D120WHCF40	8.0"L x 8.0"W x 13.5"H / Post Top / 13W 1,000L / White Finish / Clear Flemish Lens / 4000K
MCO-WINCWHCF	8.0"W x 13.25"H / Short Tail Wall Mount / Incandescent Socket / White Finish / Clear Flemish Lens
MCO-WLED13D120WHCF40	8.0"W x 13.25"H / Short Tail Wall Mount / 13W 1,000L / White Finish / Clear Flemish Lens / 4000K

Change "WH" to "BK" for black finish. See lens options below. Add "PC" for photocell (not available on post top). Also available in 30K.



Frosted Lens (FR)



Clear Lens (CL)



White Lens (WH)



Flemish Lens (CF)

## Princeton Laterns & Post Tops

Short and long tail lanterns & post tops suitable for outdoor applications in residential and commercial areas.



ITEM NO.	DESCRIPTION
MPR-LINCLEDWHWH40	8.0"Dia x 17.5"H / Long Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Lens
MPR-LLED13D120WHWH40	8.0"Dia x 13.5"H / Long Tail Wall Mount / 13W 1,000L / White Finish / White Lens / 4000K
MPR-PINCLEDWHWH40	8.0"Dia x 13.5"H / Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Lens
MPR-PLED13D120WHWH40	8.0"Dia x 13.5"H / Post Top / 13W 1,000L / White Finish / White Lens / 4000K
MPR-WINCLEDWHWH40	8.0"Dia x 13.5"H / Short Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Lens
MPR-WLED13D120WHWH40	8.0"Dia x 13.5"H / Short Tail Wall Mount / 13W 1,000L / White Finish / White Lens / 4000K

Change "WH" to "BK" for black finish. Change "WH" to "CL" for clear lens. Also available in 30K.

# OUTDOOR



## Stagecoach Lantern

Molded of durable, non-corrosive, UV resins this lantern is suitable for damp locations in commercial and residential applications.

ITEM NO.	DESCRIPTION
MSC-WINCLEDWHFR40	6.13"Dia x 6.75"Dp x 15.0"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MSC-WLED13D120WHFR40	6.13"Dia x 6.75"Dp x 15.0"H / 13W 1,000L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" or "BZ" for black or bronze finish. Add "PC" for photocell. Also available in 30K.



## Pocket Acorn

This economical, compact fixture is perfect for coastal and marine environments.

ITEM NO.	DESCRIPTION
MAPW6-INCLEDWH40	6"Dia x 9"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish
MAPW6-LED11MVWH40	6"Dia x 9"H / 11W 912L / White Finish / 4000K
MAPW6-LED13D120WH40	6"Dia x 9"H / 13W 1,000L / White Finish / 4000K

Change "WH" to "BK" for black finish. Add "PC" for photocell. Also available in 30K.



## Cottage Wall Mount

The cottage style wall mount is molded of durable, non-corrosive, UV resistant resins, and is suitable for damp locations.

ITEM NO.	DESCRIPTION
MDH5-INCLEDBKWH40	5.0"L x 5.0"W x 9.5"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / Black Finish / White Lens
MDH5-LED13D120BKWH40	5.0"L x 5.0"W x 9.5"H / 13W 1,000L / Black Finish / White Lens / 4000K

Add "PC" for photocell. Also available in 30K.



## Amhearst Lanterns & Post Tops

Short and long tail lanterns & post tops suitable for outdoor applications in residential and commercial areas.

ITEM NO.	DESCRIPTION
MAO-LINCLEDWHFR40	8"W x 25"H / Long Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MAO-LLED13D120WHFR40	8"W x 25"H / Long Tail Wall Mount / 13W 1,000L / White Finish / Frosted Lens / 4000K
MAO-PINCLEDWHFR40	8"W x 18"H / Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MAO-PLED13D120WHFR40	8"W x 18"H / Post Top / 13W 1,000L / White Finish / Frosted Lens / 4000K
MAO-WINCLEDWHFR40	8"W x 20"H / Short Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MAO-WLED13D120WHFR40	8"W x 20"H / Short Tail Wall Mount / 13W 1,000L / White Finish / Frosted Lens / 4000K

Change "WH" to "BK" for black finish. Change "FR" to "WH" or "CL" for white or clear lens. Add "PC" for photocell (not available on post top). Also available in 30K.

# OUTDOOR



## Hexagon Lanterns & Post Tops

Short and long tail lanterns & post tops suitable for outdoor applications in residential and commercial areas.

ITEM NO.	DESCRIPTION
MHO-LINCLEDDWHCL40	9.0"Dia x 21.5"H / Long Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHO-LLED13D120WHCL40	9.0"Dia x 21.5"H / Long Tail Wall Mount / 13W 1,000L / White Finish / Clear Lens / 4000K
MHO-PINCLEDDWHCL40	9.0"Dia x 15.5"H / Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHO-PLED13D120WHCL40	9.0"Dia x 15.5"H / Post Top / 13W 1,000L / White Finish / Clear Lens / 4000K
MHO-WINCLEDDWHC40	9"Dia x 16"H / Short Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHO-WLED13D120WHC40	9"Dia x 16"H / Short Tail Wall Mount / 13W 1,000L / White Finish / Clear Lens / 4000K

Change "WH" to "BK" for black finish. Add "PC" for photocell (not available on post top). Also available in 30K.



## Hatch Lanterns & Post Tops

Short and long tail lanterns & post tops suitable for outdoor applications in residential and commercial areas.

ITEM NO.	DESCRIPTION
MHT-PINCLEDDWHCL40	8"L x 8"W x 16"H / Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHT-PLED13D120WHCL40	8"L x 8"W x 16"H / Post Top / 13W 1,000L / White Finish / Clear Lens / 4000K
MHT-WINCLEDDWHCL40	6.5"W x 8.5"Dp x 10.5"H / Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHT-WLED13D120WHCL40	6.5"W x 8.5"Dp x 10.5"H / Wall Mount / 13W 1,000L / White Finish / Clear Lens / 4000K
MHT-SINCLEDDWHCL40	8.0"W x 8.5"Dp x 16.0"H / Short Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHT-SLED13D120WHCL40	8.0"W x 8.5"Dp x 16.0"H / Short Tail Wall Mount / 13W 1,000L / White Finish / Clear Lens / 4000K
MHT-LINCLEDDWHC40	8.0"W x 8.5"Dp x 21.25"H / Long Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MHT-LLED13D120WHCL40	8.0"W x 8.5"Dp x 21.25"H / Long Tail Wall Mount / 13W 1,000L / White Finish / Clear Lens / 4000K

Change "WH" to "BK" for black finish. Add "PC" for photocell (not available on post top). Also available in 30K.



## Kingston Lanterns & Post Tops

Short and long tail lanterns & post tops suitable for outdoor applications in residential and commercial areas.

ITEM NO.	DESCRIPTION
MKR-LINCLEDDWHCL40	8.0"Dia x 21.13"H / Long Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MKR-LLED13D120WHCL40	8.0"Dia x 21.13"H / Long Tail Wall Mount / 13W 1,000L / White Finish / Clear Lens / 4000K
MKR-PINCLEDDWHCL40	8.0"Dia x 14.75"H / Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MKR-PLED13D120WHCL40	8.0"Dia x 14.75"H / Post Top / 13W 1,000L / White Finish / Clear Lens / 4000K
MKR-WINCLEDDWHCL40	8.0"Dia x 15.5"H / Short Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Clear Lens
MKR-WLED13D120WHCL40	8.0"Dia x 15.5"H / Short Tail Wall Mount / 13W 1,000L / White Finish / Clear Lens / 4000K

Change "WH" to "BK" for black finish. Change "CL" to "WH" for white lens. Add "PC" for photocell (not available on post top). Also available in 30K.



# OUTDOOR



MTO

MTOL  
(shown with brass finial)

## Tudor Lanterns & Post Tops

Long tail lanterns & post tops suitable for outdoor applications in residential and commercial areas.

ITEM NO.	DESCRIPTION
MTO-LINCLEDKFR40	7.75"W x 8.0"Dp x 17.0"H / Long Tail Wall Mount / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / Black Finish / Frosted Bevel Lens
MTO-LLED13D120BKFR40	7.75"W x 8.0"Dp x 17.0"H / Long Tail Wall Mount / 13W 1,000L / Black Finish / Frosted Bevel Lens / 4000K
MTO-PINCLEDWHFR40	7.75"L x 7.75"W x 12.5"H / Post Top / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Bevel Lens
MTO-PLED13D120WHFR40	7.75"L x 7.75"W x 12.5"H / Post Top / 13W 1,000L / White Finish / Frosted Bevel Lens / 4000K

Change "WH" to "BK" for black finish. See lens option on page 74. Add "BF" for brass finial. Add "PC" for photocell (not available on post top). Also available in 30K.

## Glass Chimney Lanterns & Post Tops

Short tail lanterns & post top suitable for outdoor applications in residential and commercial areas.



MGCP

MGCW

ITEM NO.	DESCRIPTION
MGC-PINCBKFR	10"L x 10"W x 17"H / Post Top / Incandescent Socket / Black Finish / Frosted Lens
MGC-P-LED13D120BKFR40	10"L x 10"W x 17"H / Post Top / 13W 1,000L / Black Finish / Frosted Lens / 4000K
MGC-WINCBKFR	10.0"W x 10.25"Dp x 18.0"H / Wall Mount / Incandescent Socket / Black Finish / Frosted Lens
MGC-W-LED13D120BKFR40	10.0"W x 10.25"Dp x 18.0"H / Wall Mount / 13W 1,000L / Black Finish / Frosted Lens / 4000K

Change "FR" to "CL" for clear lens. Add "BF" for brass finial. Also available in 30K.

## Imperial Post Tops

Imperial post tops are suitable for wet locations and fit most 3" diameter posts.



MIO10

MIO13  
(shown with brass finial)

ITEM NO.	DESCRIPTION
MIO-P10INCLEDWHFR40	10.5"L x 10.5"W x 18.0"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MIO-P10-LED23D120WHFR40	10.5"L x 10.5"W x 18.0"H / 23W 1,900L / White Finish / Frosted Lens / 4000K
MIO-P13INCLEDWHFR40	13"L x 13"W x 18"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / Frosted Lens
MIO-P13-LED23D120WHFR40	13"L x 13"W x 18"H / 23W 1,900L / White Finish / Frosted Lens / 4000K

Change "FR" to "CL" for clear lens. Change "WH" to "BK" for black finish. Add "BF" for brass finial. Also available in 30K.

## Fitter Neck Pocket Wall Mount

Classic globe and jar style compact wall mounts suitable for wet locations.



Jar (J)

Globe (G)

Rounded Jar (R)

Jelly Jar (JJ)

ITEM NO.	DESCRIPTION
MFN-INCLEDWHRWH40	4.5"Dia x 8.0"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Rounded Jar
MFN-LED13D120WHRWH40	4.5"Dia x 8.0"H / 13W 1,000L / White Finish / White Rounded Jar / 4000K
MFN-LED11MVWHRWH40	4.5"Dia x 8.0"H / 11W 912L / White Finish / White Rounded Jar / 4000K
MFN-INCLEDWHJWH40	4.5"Dia x 9.25"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Jar
MFN-LED13D120WHJWH40	4.5"Dia x 9.25"H / 13W 1,000L / White Finish / White Jar / 4000K
MFN-LED11MVWHJWH40	4.5"Dia x 9.25"H / 11W 912L / White Finish / White Jar / 4000K
MFN-INCLEDWHGWH40	6"Dia x 8"H / Incandescent Socket / 9.5W 800L 4000K A19 Lamp Included / White Finish / White Globe
MFN-LED13D120WHGWH40	6"Dia x 8"H / 13W 1,000L / White Finish / White Globe / 4000K
MFN-LED11MVWHGWH40	6"Dia x 8"H / 11W 912L / White Finish / White Globe / 4000K

Change "WH" to "BK" for black finish. Consult for lens options. Add "PC" for photocell (not available with "11MV" option). Also available in 30K.

# OUTDOOR



Shown with mounting arm.

## Dusk To Dawn

Built-in photocell (included). Great for farms, loading docks, parking lots, and warehouses.

ITEM NO.	DESCRIPTION
D2D12-LED45MVBZ50	15.75"L x 8.98"Dia x 7.65"H / 45W 6,400L / Bronze Finish / 5000K
D2D12-LED70MVBZ50	15.75"L x 8.98"Dia x 7.65"H / 70W 9,600L / Bronze Finish / 5000K

### Accessories & Replacement Parts

D2DARMKIT	Mounting Arm Kit For Pole Mounting
A-MS-PSUNVB1	Replacement Photocell / Field Installed, Or By Factory Upon Request

Change "BZ" to "GY" for silver gray finish. Also available in 40K.

## Sensor Ready Wall Pack

This great value sensor ready wall pack has additional shield, photocell, and emergency options. Ideal for security, accent, and perimeter lighting.

ITEM NO.	DESCRIPTION
MIMDWPKSR-LED45DMVBZ50	14.21"L x 9.25"W x 7.95"Dp / Medium Wall Pack / 45W 5,300L / Standard Bronze Finish / 5000K
MIMDWPKSR-LED70DMVBZ50	14.21"L x 9.25"W x 7.95"Dp / Medium Wall Pack / 70W 8,100L / Standard Bronze Finish / 5000K
MILGWPKSR-LED90DMVBZ50	18.0"L x 10.54"W / Large Wall Pack / 90W 9,950L / Standard Bronze Finish / 5000K
MILGWPKSR-LED135DMVBZ50	18.0"L x 10.54"W / Large Wall Pack / 135W 15,550L / Standard Bronze Finish / 5000K

Add "EM" for emergency. Add "OS" for occupancy sensor. Add "PC" for photocell. Also available in 40K (special order).

## Mini Wall Pack

Perfect for security, entryways, stairways, storage, and perimeter areas.

ITEM NO.	DESCRIPTION
MISMROWPK-LED17MV50	8.38"L x 5.48"W x 3.52"Dp / 17W 2,000L / Standard Bronze Finish / 5000K
MISMROWPK-LED17MV50PC	8.38"L x 5.48"W x 3.52"Dp / 17W 2,000L / Standard Bronze Finish / 5000K / Photocell
MISMROWPK-LED25MV50	8.38"L x 5.48"W x 3.52"Dp / 25W 2,700L / Standard Bronze Finish / 5000K
MISMROWPK-LED25MV50PC	8.38"L x 5.48"W x 3.52"Dp / 25W 2,700L / Standard Bronze Finish / 5000K / Photocell

Also available in 30K.

## Sensor Ready Cut-Off Wall Pack

This full cut-off wall pack features additional photocell and emergency options. Great for security, accent, and perimeter lighting.

ITEM NO.	DESCRIPTION
MIMDCOWPKSR-LED45DMVBZ50	14.21"L x 8.8"W / Medium Wall Pack / 45W 4,900L / Standard Bronze Finish / 5000K
MIMDCOWPKSR-LED70DMVBZ50	14.21"L x 8.8"W / Medium Wall Pack / 70W 7,500L / Standard Bronze Finish / 5000K
MILGCOWPKSR-LED90DMVBZ50	18.1"L x 11.24"W x 10.53"H / Large Wall Pack / 90W 9,700L / Standard Bronze Finish / 5000K
MILGCOWPKSR-LED135DMVBZ50	18.1"L x 11.24"W x 10.53"H / Large Wall Pack / 135W 14,500L / Standard Bronze Finish / 5000K

Add "EM" for emergency. Add "OS" for occupancy sensor. Add "PC" for photocell. Also available in 40K (special order).

## Decorative Cut-Off Wall Pack

A stylish alternative to standard wall packs, this round wall pack is great for tunnels, loading docks, and bridges.

ITEM NO.	DESCRIPTION
DCSHM-36W-50K-BZ-D1	18.0"L x 7.13"H / 36W 4,633L / Standard Bronze Finish / 5000K
DCSHMUD-12W-48W-50K-BZ-D1	18.0"L x 7.13"H / 12W Up 48W Down 6,178L / Standard Bronze Finish / 5000K
DCSHMUD-12W-60W-50K-BZ-D1	18.0"L x 7.13"H / 12W Up 60W Down 7,723L / Standard Bronze Finish / 5000K

Add "EM" for emergency. Add "MS" for motion sensor or "MS-DS2" for motion sensor with bi-level dimming. Change "D1" to "D2" for step dimming or "V1" for 480/347 input. Also available in 27K, 30K, 35K, 40K, & 55K.



# OUTDOOR

## 12" Area Light



This highly efficient, long-life area light is perfect for auto dealerships, parking lots, walkways, roadways, and campuses.



ITEM NO.	DESCRIPTION
SAL-12LED70DMVBZ50	12.4"L x 11.26"W / 70W 9,000L / Standard Bronze Finish / Type 3 Distribution / 5000K
SAL-12LED105DMV50	12.4"L x 11.26"W / 105W 13,400L / Standard Bronze Finish / Type 3 Distribution / 5000K

Consult for other finish options. Add "SP" for surge protection. Also available in 40K (special order).

## Sensor Ready 16" & 25" Area Light



This sensor-ready version of our 12" area light has optional photocell and occupancy sensor capabilities. With multiple different types of distribution available, this fixture is perfect for grocery stores, parking lots, roadways, and facade lighting.



ITEM NO.	DESCRIPTION
SALSR-16LED150DMV50	15.79"L x 13.0"W / 150W 19,700L / Standard Bronze Finish / Type 3 Distribution / 5000K
SALSR-16LED150DMVT550	15.79"L x 13.0"W / 150W 21,150L / Standard Bronze Finish / Type 5 Distribution / 5000K
SALSR-16LED200DMV50	15.79"L x 13.0"W / 200W 26,200L / Standard Bronze Finish / Type 3 Distribution / 5000K
SALSR-16LED200DMVT550	15.79"L x 13.0"W / 200W 27,200L / Standard Bronze Finish / Type 5 Distribution / 5000K
SALSR-25LED250DMV50	25.04"L x 13.4"W / 250W 33,250L / Standard Bronze Finish / Type 3 Distribution / 5000K
SALSR-25LED250DMVT550	25.04"L x 13.4"W / 250W 35,250L / Standard Bronze Finish / Type 5 Distribution / 5000K
SALSR-25LED300DMV50	25.04"L x 13.4"W / 300W 39,300L / Standard Bronze Finish / Type 3 Distribution / 5000K
SALSR-25LED300DMVT550	25.04"L x 13.4"W / 300W 42,300L / Standard Bronze Finish / Type 5 Distribution / 5000K

Consult for other finish options. Add "OS" for occupancy sensor. Add "SP" for surge protection. Consult for photocell option. Also available in 40K (special order).

ITEM NO.	DESCRIPTION
<b>Area Light Accessories</b>	
SAL-SQ-ARM	Square Pole Mounting Arm For SAL Area Lights / Bronze Finish
SAL-RD-ARM	Round Pole Mounting Arm For SAL Area Lights / Bronze Finish
SAL-SF	Slip Fitter Mounting Arm For SAL Area Lights / Bronze Finish
SAL-WALL-ARM	Wall Mounting Arm For SAL Area Lights / Bronze Finish
A-SC-AL01-150W-BA	Backlight Control (order 2 for 250W & 300W)

Mounting Arm



Slip Fitter Mount



Wall Mounting Arm



# OUTDOOR



## Small Flood Light

This compact but powerful flood light is suitable for wet location, and perfect for landscape lighting applications.

ITEM NO.	DESCRIPTION
LED-2350048UNV750BZ-40C	8.9"L x 5.0"W x 1.9"Dp / 48W 5,563L / Bronze Finish / 5000K
LED-2375069UNV750BZ-40C	12.04"L x 6.41"W x 2.9"Dp / 69W 8,579L / Bronze Finish / 5000K

Consult for U bracket and slip fitter mounting options.

## Mini Flood Light

This miniature flood light is suitable for wet locations, and features 3 different mounting options.

ITEM NO.	DESCRIPTION
FLMM-5LED15MVBZ50	4.72"L x 1.45"W x 2.95"H / 15W 1,500L / Bronze Finish / 5000K
FLMM-7LED30MVBZ50	7.08"L x 1.75"W x 4.42"H / 30W 3,000L / Bronze Finish / 5000K
FLMM-8LED45MVBZ50	8.26"L x 2.45"W x 5.16"H / 45W 5,400L / Bronze Finish / 5000K

Consult for knuckle, trunnion, and wall mounting options. Also available in 30K & 40K.



## Medium & Large Flood Light

High performance flood lights with multiple mounting options and cast aluminum housing. Ideal for parking lots, walkways, campuses, car dealerships, and office complexes.

ITEM NO.	DESCRIPTION
FLM-6LED15DMVBZ50	6.0"L x 2.6"W x 3.82"H / 15W 2,000L / Bronze Finish / 5000K
FLM-6LED27DMVBZ50	6.0"L x 2.6"W x 3.82"H / 27W 3,600L / Bronze Finish / 5000K
FLM-8LED45DMVBZ50	8.0"L x 3.1"W x 4.8"H / 45W 5,650L / Bronze Finish / 5000K
FLM-8LED60DMVBZ50	8.0"L x 3.1"W x 4.8"H / 60W 7,450L / Bronze Finish / 5000K
FLM-11LED70DMVBZ50	11.06"L x 4.9"W x 6.08"H / 70W 8,900L / Bronze Finish / 5000K
FLM-11LED100DMVBZ50	11.06"L x 4.9"W x 6.08"H / 100W 13,300L / Bronze Finish / 5000K
FLM-15LED135DMVBZ50	14.5"L x 4.4"W x 8.98"H / 135W 17,800L / Bronze Finish / 5000K
FLM-15LED200DMVBZ50	14.5"L x 4.4"W x 8.98"H / 200W 26,000L / Bronze Finish / 5000K


Change "DMV" to "DHV" for 347-480V driver (70W, 135W & 200W only). Consult for 40K. See mounting options & accessories below.



## FLM Mounting Options & Accessories

(Add To The End Of Part Number)

ITEM NO.	DESCRIPTION
<b>6" &amp; 8" Options</b>	
KN	Knuckle Mount
TR	Trunnion Mount
PC	Photocell
<b>11" &amp; 15" Options</b>	
SF	Slip Fitter Mount
YK	Yoke Mount





# OUTDOOR



## Architectural Tall Bollard

Almost 12 feet tall with 4 feet of durable acrylic diffuser, this bollard makes a bold statement. This bollard is bolted with a mounting plate provided by the customer or an anchorage unit made of hot-dip galvanized steel.

### ITEM NO.

### DESCRIPTION

CASSIOPEIA	7.0"Dia x 90.55"H / 80W / Gun Metal / 4000K
CASSIOPEIAGMRGB	7.0"Dia x 90.55"H / 80W / Gun Metal / 4000K / Red, Green, Blue



## 8" Commercial Grade Bollard

This heavy-duty bollard features an aluminum construction housing providing corrosion and vandal resistance. Ideal for lighting pedestrian walkways and accenting exterior building grounds.

### ITEM NO.

### DESCRIPTION

GRPL-10A018UNV750-S	8"Dia x 36"H / Round Bollard / 18W 2,035L / Bronze Finish / 5000K
GRPL-10A036UNV750-S	8"Dia x 36"H / Round Bollard / 36W 3,960L / Bronze Finish / 5000K
GRPL-10A018UNV750-C	8"Dia x 36"H / Flat Bollard / 18W 2,035L / Bronze Finish / 5000K
GRPL-10A036UNV750-C	8"Dia x 36"H / Flat Bollard / 26W 3,960L / Bronze Finish / 5000K

Also available in 4000K.



## 6" Commercial Grade Bollard

This attractive 6" diameter bollard is perfect for building entryways, walking paths, pedestrian plazas, and any other location requiring a low mounting height light source.

### ITEM NO.

### DESCRIPTION

BOLMA6-LED26MVBZ50	5.5"Dia x 42"H / 26W 3,100L / Bronze Finish / 5000K
--------------------	---

# OUTDOOR



## Round Post Top

Contemporary and attractive, this post top features a modern look with a high lumen output. Consult for sensor and photocell options.

ITEM NO.	DESCRIPTION
LED-9800053UNV740T5BZ-40C	17.3"Dia x 22.3"H / 53W 6,814L / Type 5 Distribution / Bronze Finish / 4000K
LED-9800078UNV740T5BZ-40C	17.3"Dia x 22.3"H / 78W 9,506L / Type 5 Distribution / Bronze Finish / 4000K
LED-9800143UNV740T5BZ-40C	17.3"Dia x 22.3"H / 143W 15,408L / Type 5 Distribution / Bronze Finish / 4000K

Consult for other color temperature options.



## Steel Poles (Consult For Pricing)

- ▶ 12 top holes w/ polycarbonate lexan brushings
- ▶ Reinforced hand hold cover
- ▶ Anchor bolts and template included
- ▶ Easily secured base cover
- ▶ Bronze polyester powder-coat finish
- ▶ Meets ASTM 500 standard
- ▶ Pole cap included

Tenon Top Adaptor



MITVA4  
MITVA5

ITEM NO.	DESCRIPTION	Shaft Size	Gage	Bolt Circle	Bolt Size	Weight lbs.
MIPK204SQNT	20 ft. 4 x 4 Square 11 Gauge Pole	20	11	9½"	¾" x 30"	146
MIPK254SQNT	25 ft. 4 x 4 Square 11 Gauge Pole	25	11	9½"	¾" x 30"	180
MIPK305SQNT	30 ft. 5 x 5 Square 11 Gauge Pole	30	11	11"	1" x 36"	290

Pole does not include tenon. Poles can be cut to any length.


## Pole Accessories:

2 Light Square Bullhorn




▶ MITV2\*

4 Light Square Bullhorn



▶ MITVC4\*

Pole Top Cap



▶ MIP45QBPC  
▶ MIP55QBPC

Pole Base Cover



▶ MIP4BCPBZ-A  
▶ MIP5BCPBZ-A

Anchor Bolts



▶ MIABK3/4IX201-F  
▶ MIABK1IX361-F

Wall Mount Vertical



▶ MIABK3/4IX201-F  
▶ MIABK1IX361-F

\*Requires MITVA4 or MITVA5

# EXIT SIGNS



w/ Remote Capability



## Compact LED EXIT Sign

ITEM NO.	DESCRIPTION
EZRXTU2GWEM	11.63"L x 7.88"H x 1.63"Dp / Universal Single Or Double Face / Green Letters / Battery Backup
EZRXTU2RWEM	11.63"L x 7.88"H x 1.63"Dp / Universal Single Or Double Face / Red Letters / Battery Backup

## Thermoplastic LED EXIT Sign

ITEM NO.	DESCRIPTION
EZXTEU2GWEM	12.75"L x 7.5"H x 1.75"Dp / Universal Single Or Double Face / Green Letters / White Housing / Battery Backup
EZXTEU2GWEMRC	12.75"L x 10.94"H x 2.5"Dp / Universal Single Or Double Face / Green Letters / White Housing / Battery Backup / Remote Capable
EZXTEU2RWEM	12.75"L x 7.5"H x 1.75"Dp / Universal Single Or Double Face / Red Letters / White Housing / Battery Backup
EZXTEU2RWEMRC	12.75"L x 10.94"H x 2.5"Dp / Universal Single Or Double Face / Red Letters / White Housing / Battery Backup / Remote Capable

Consult for thin thermoplastic EXIT sign.

## Thin Die-Cast LED EXIT Sign

ITEM NO.	DESCRIPTION
KZXTEU1GAEM	11.82"L x 8.19"H x 0.88"Dp / Single Face / Green Letters / Aluminum Housing / Battery Backup
KZXTEU1RAEM	11.82"L x 8.19"H x 0.88"Dp / Single Face / Red Letters / Aluminum Housing / Battery Backup

## Thermoplastic Edgelit LED EXIT Sign

ITEM NO.	DESCRIPTION
PLELRXTU1RCAEM	14.44"L x 11.94"H / Single Face / Silver Housing / Red Letters / Clear Panel / Battery Backup
PLELRXTU1RCWEM	14.44"L x 11.94"H / Single Face / White Housing / Red Letters / Clear Panel / Battery Backup

## Aluminum Edgelit LED EXIT Sign

ITEM NO.	DESCRIPTION
ELXTEU1GCAEM	13.75"L x 11.88"H / Single Face / Aluminum Housing / Green Letters / Clear Panel / Battery Backup
ELXTEU1RCAEM	13.75"L x 11.88"H / Single Face / Aluminum Housing / Red Letters / Clear Panel / Battery Backup

# EXIT SIGNS



## Recessed Aluminum Edgelit LED EXIT Sign

ITEM NO.	DESCRIPTION
RELZXTE1GCAEM	14.56"L x 10.56"H x 0.38"Dp / Single Face / Aluminum Housing / Green Letters / Clear Panel / Battery Backup
RELZXTE1RCAEM	14.56"L x 10.56"H x 0.38"Dp / Single Face / Aluminum Housing / Red Letters / Clear Panel / Battery Backup
RELZXTE2GMAEM	14.56"L x 10.56"H x 0.38"Dp / Double Face / Aluminum Housing / Green Letters / Mirrored Panel / Battery Backup
RELZXTE2RMAEM	14.56"L x 10.56"H x 0.38"Dp / Double Face / Aluminum Housing / Red Letters / Mirrored Panel / Battery Backup



## Compact Wet Location LED EXIT Sign

ITEM NO.	DESCRIPTION
WLEZXTEU1GGEMCW	12.5"L x 9.25"H x 2.5"Dp / Single Face / Green Letters / Gray Housing / Battery Backup / Cold Weather
WLEZXTEU1RGEMCW	12.5"L x 9.25"H x 2.5"Dp / Single Face / Red Letters / Gray Housing / Battery Backup / Cold Weather
WLEZXTEU2GGEMCW	12.5"L x 9.25"H x 2.5"Dp / Double Face / Green Letters / Gray Housing / Battery Backup / Cold Weather
WLEZXTEU2RGEMCW	12.5"L x 9.25"H x 2.5"Dp / Double Face / Red Letters / Gray Housing / Battery Backup / Cold Weather



## NEMA4X/NSF Exit Sign

This unit is certified for wet locations and certified by UL to meet U.S. safety and sanitation requirements ideal for food service environments.

ITEM NO.	DESCRIPTION
INDWLEZU1RBEM	14.75"L x 10.0"H x 6.0"Dp / Single Face / Red Letters / Black Housing / Battery Backup
INDWLEZU2RBEM	14.75"L x 10.0"H x 6.0"Dp / Double Face / Red Letters / Black Housing / Battery Backup
INDWLEZU1GBEM	14.75"L x 10.0"H x 6.0"Dp / Single Face / Green Letters / Black Housing / Battery Backup
INDWLEZU2GBEM	14.75"L x 10.0"H x 6.0"Dp / Double Face / Green Letters / Black Housing / Battery Backup

Add "SDT" for self-diagnostics. Change "B" to "W" or "G" for white or gray housing. Add "TP" for tamper-proof.



## Hazardous Location Exit Sign

Ideal for areas that use chemicals that create a hazardous environment. Rated for class 1, division 2, groups A, B, C, & D.

ITEM NO.	DESCRIPTION
HLWLEZU1RGEM	14.75"L x 10.0"H x 6.0"Dp / Single Face / Red Letters / Gray Housing / Battery Backup
HLWLEZU2RGEM	14.75"L x 10.0"H x 6.0"Dp / Double Face / Red Letters / Gray Housing / Battery Backup
HLWLEZU1GGEM	14.75"L x 10.0"H x 6.0"Dp / Single Face / Green Letters / Gray Housing / Battery Backup
HLWLEZU2GGEM	14.75"L x 10.0"H x 6.0"Dp / Double Face / Green Letters / Gray Housing / Battery Backup

Add "SDT" for self-diagnostics. Add "TP" for tamper-proof.



# EXIT COMBOS



## All LED EXIT & Emergency Combo

ITEM NO.	DESCRIPTION
LEDCXTEU2RW	20.31"L x 8.63"H x 4.31"Dp / Universal Single Or Double Face / Red Letters / White Housing / Battery Backup / LED Lamp Heads
LEDCXTEU2RWRC	20.31"L x 8.63"H x 4.31"Dp / Universal Single Or Double Face / Red Letters / White Housing / Battery Backup / LED Lamp Heads / Remote Capable

Change "W" to "B" for black housing.

## LED EXIT & Incandescent Emergency Combo



ITEM NO.	DESCRIPTION
CXTEU2GW	20.31"L x 8.63"H x 4.31"Dp / Universal Single Or Double Face / Green Letters / White Housing / Battery Backup
CXTEU2GWRC	20.31"L x 8.63"H x 4.31"Dp / Universal Single Or Double Face / Green Letters / White Housing / Battery Backup / Remote Capable
CXTEU2RW	20.31"L x 8.63"H x 4.31"Dp / Universal Single Or Double Face / Red Letters / White Housing / Battery Backup
CXTEU2RWRC	20.31"L x 8.63"H x 4.31"Dp / Universal Single Or Double Face / Red Letters / White Housing / Battery Backup / Remote Capable

Change "W" to "B" for black housing.

## Low Profile All LED EXIT & Emergency Combo



ITEM NO.	DESCRIPTION
CEU3RW	16.0"L x 7.94"H x 1.94"Dp / Universal Single Or Double Face / Red Letters / White Face
CEU3GW	16.0"L x 7.94"H x 1.94"Dp / Universal Single Or Double Face / Green Letters / White Face

Change "W" to "B" for black housing.



## Lightpipe LED EXIT & Emergency Combo

ITEM NO.	DESCRIPTION
CLPU2GWRC	12.5"L x 9.125"H x 1.88"Dp / Universal Single Or Double Face / Green Letters / White Housing / Remote Capable
CLPU2RWRC	12.5"L x 9.125"H x 1.88"Dp / Universal Single Or Double Face / Red Letters / White Housing / Remote Capable

Change "W" to "B" for black housing.

# EXIT COMBOS



Lit when emergency is activated.

## Low Level Mounted All LED Exit & Emergency

Great for theaters, hotels, and residential care facilities.

ITEM NO.	DESCRIPTION
LCTXTEU1RW	14.13"L x 10.13"H x 1.0"Dp / Single Face / Red Letters / White Housing
LCTXTEUGW	14.13"L x 10.13"H x 1.0"Dp / Single Face / Green Letters / White Housing

Change "W" to "B" for black housing.

## All LED NEMA4X/NSF Exit & Emergency Combo

This unit is certified for wet locations and certified by UL to meet U.S. safety and sanitation requirements ideal for food service environments.



ITEM NO.	DESCRIPTION
INDCWLEZU1R615B	14.88"L x 14.19"H x 6.0"Dp / Single Face / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / Red Letters 6V 15W Remote Capacity / Black Housing
INDCWLEZU1R628B	14.88"L x 14.19"H x 6.0"Dp / Single Face / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / Red Letters / 6V 28W Remote Capacity / Black Housing
INDCWLEZU2R612B	14.88"L x 14.19"H x 6.0"Dp / Double Face / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / Red Letters / 6V 12W Remote Capacity / Black Housing

Add "SDT" for self-diagnostics. Change "6" to "12" for 12 volts. Change "R" to "G" for green letters. Add "TP" for tamper-proof.

## All LED Hazardous Exit & Emergency Combo

Ideal for areas that use chemicals that create a hazardous environment. Rated for class 1, division 2, groups A, B, C, & D.



ITEM NO.	DESCRIPTION
HLCWLEZU1R615G	14.88"L x 14.19"H x 6.0"Dp / Single Face / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / Red Letters 6V 15W Remote Capacity / Gray Housing
HLCWLEZU1R628G	14.88"L x 14.19"H x 6.0"Dp / Single Face / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / Red Letters / 6V 28W Remote Capacity / Gray Housing
HLCWLEZU2R612G	14.88"L x 14.19"H x 6.0"Dp / Double Face / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / Red Letters / 6V 12W Remote Capacity / Gray Housing


Add "SDT" for self-diagnostics. Change "6" to "12" for 12 volts. Change "R" to "G" for green letters. Add "TP" for tamper-proof.

Ask Us About Chicago & New York Approved Exit Signs, Emergencies, and Combos!



# EMERGENCY

## LED Thermoplastic Emergency Unit



ITEM NO.	DESCRIPTION
LEDR1	12.0"L x 4.56"H x 2.5"Dp / 2 LED Remote Heads / 3.6V 1W (8 LEDs x 0.125W) Per Head / White Housing
LEDR1B	12.0"L x 4.56"H x 2.5"DP / 2 LED Remote Heads / 3.6V 1W (8 LEDs x 0.125W) Per Head / Black Housing
LEDR1SDT	12.0"L x 4.56"H x 2.5"Dp / 2 LED Remote Heads / 3.6V 1W (8 LEDs x 0.125W) Per Head / White Housing / Self Diagnostics

## Remote Capable LED Thermoplastic Emergency Unit



ITEM NO.	DESCRIPTION
LEDR5HO	12.0"L x 4.56"H x 2.5"Dp / 2 LED Remote Heads / 3.6V 1W (8 LEDs x 0.125W) Per Head / White Housing / Remote Capable
LEDR5HOSDT	12.0"L x 4.56"H x 2.5"Dp / 2 LED Remote Heads / 3.6V 1W (8 LEDs x 0.125W) Per Head / White Housing / Remote Capable / Self Diagnostics

Add "B" after "HO" for black housing.

## Fixed Optic Emergency Unit



ITEM NO.	DESCRIPTION
FLEDR2	11.83"L x 5.13"H x 2.38"Dp / 2 Fixed 6V 5.4W LED Lamp Heads / White Housing

## Adjustable Optics LED Emergency Unit



ITEM NO.	DESCRIPTION
LEDR2	9.5"L x 4.63"H x 2.25"Dp / 2 Adjustable LED Remote Heads / 3.6V 1W (8 LEDs x 0.125W) Per Head / White Housing
LEDR2B	9.5"L x 4.63"H x 2.25"Dp / 2 Adjustable LED Remote Heads / 3.6V 1W (8 LEDs x 0.125W) Per Head / Black Housing

## LED Semi-Recessed Thermoplastic Emergency Unit



ITEM NO.	DESCRIPTION
RMR16LED	14.38"L x 5.63"H x 4.25"Dp / 2 Fully Adjustable Semi-Recessed 6V 3.3W High Lumen MR-16 White LED Lamp Heads / Gray Housing

Add "B" after "16" for black finish. Consult for MR-16 version.

## Remote Capable Incandescent Emergency Unit



ITEM NO.	DESCRIPTION
DXR610	12.75"L x 3.25"W x 14.19"H / 6V 100W / 7.2W Lamps Standard
DXR125	12.63"L x 5.0"W x 14.0"H / 12V 50W / 9W Lamps Standard

# EMERGENCY - WET LOCATION



## Wet Location Semi-Recessed LED Emergency Unit

ITEM NO.	DESCRIPTION
RMR16WPLED	14.38"L x 5.63"H x 4.25"Dp / 2 Fully Adjustable 3.3W Semi-Recessed High Lumen White LED Lamp Heads / Gray Housing

Add "B" after "16" for black housing. Consult for MR-16 version.



## Decorative Outdoor LED Ac/Emergency Unit

ITEM NO.	DESCRIPTION
DBELACEMHLBRSDTPC	6.56"L x 10.5"H x 3.63"Dp / 4.8V 12W (2 LEDs x 6W) Per Unit / Bronze Housing / Self Diagnostics / Photocell Sensor
DBEACEMHLBRSDTCWPC	6.56"L x 10.5"H x 3.63"Dp / 4.8V 12W (2 LEDs x 6W) Per Unit / Bronze Housing / Self Diagnostics / Cold Weather / Photocell Sensor



## Wet Location Remote Capable LED Emergency Unit

ITEM NO.	DESCRIPTION
LEDTFX2	9.31"L x 12.19"H x 3.5"Dp / 9.6V 1.875W (15 LEDs x 0.125W) Per Head / Gray Housing

## LED NEMA4X/NSF Emergency Unit

This unit is certified for wet locations and certified by UL to meet U.S. safety and sanitation requirements ideal for food service environments.



ITEM NO.	DESCRIPTION
INDEM16615B	14.5"L x 6.25"H x 6.5"Dp / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / 6V 15W Remote Capacity / Black Housing

Add "SDT" for self-diagnostics. Change "B" to "W" or "G" for white or gray housing. Change "6" to "12" for 12 volts. Add "TP" for tamper-proof. Add "CW" for cold weather.

## LED Hazardous Location Emergency Unit

Ideal for areas that use chemicals that create a hazardous environment. Rated for class 1, division 2, groups A, B, C, & D.



ITEM NO.	DESCRIPTION
HLEMR16615G	14.5"L x 6.25"H x 6.5"Dp / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / 6V 15W Remote Capacity / Gray Housing

Add "SDT" for self-diagnostics. Change "6" to "12" for 12 volts. Add "TP" for tamper-proof. Add "CW" for cold weather.



# REMOTE HEADS



## Wet Location Remote Capable LED Emergency Unit

ITEM NO.	DESCRIPTION
RH26V5.4W	9.25"L x 5.5"H x 4.25"Dp / 2 Incandescent Indoor Remote Heads / 6V 5.4W / White Housing
RH2WP6V7.2W	4.5"Dia x 7.0"H / 2 Incandescent Outdoor Remote Heads / 6V 7.2W / Gray Housing
RHLED1MV	5.88"L x 4.88"H x 4.5"Dp / 1 LED Indoor Remote Head / Multivolt 1W (8 LEDs x 0.125W) Per Head / Gray Housing
RHLED1MVHL	5.88"L x 4.88"H x 4.5"Dp / 1 LED Indoor Remote Head / Multivolt 1W (12 LEDs x 0.125W) Per Head / Gray Housing
RHLED1PWPMV	4.25"Dia x 6.63"H / 1 LED Outdoor Remote Head / Multivolt 1W (8 LEDs x 0.125W) Per Head / Polycarbonate Housing / Gray Housing
RHLED1PWPMVHL	4.25"Dia x 6.63"H / 1 LED Outdoor Remote Head / Multivolt 1W (12 LEDs x 0.125W) Per Head / Polycarbonate Gray Housing
RHLED2MV	8.5"L x 4.88"H x 4.5"Dp / 2 LED Indoor Remote Heads / Multivolt 1W (8 LEDs x 0.125W) Per Head / Gray Housing
RHLED2MVHL	8.5"L x 4.88"H x 4.5"Dp / 2 LED Indoor Remote Heads / Multivolt 1.5W (12 LEDs x 0.125W) Per Head / Gray Housing
RHLED2PWPMV	10.38"Dia x 6.75"H / 2 LED Outdoor Remote Heads / Multivolt 1W (8 LEDs x 0.125W) Per Head / Polycarbonate Gray Housing
RHLED2PWPMVHL	10.38"Dia x 6.75"H / 2 LED Outdoor Remote Heads / Multivolt 1.5W (12 LEDs x 0.125W) Per Head / Polycarbonate Gray Housing

For other options and accessories, see specification sheets.

## LED NEMA4X/NSF Remote Head

This unit is certified for wet locations and certified by UL to meet U.S. safety and sanitation requirements ideal for food service environments.



ITEM NO.	DESCRIPTION
INDRHLED161B	9.63"L x 5.5"H x 4.88"Dp / 1 Fully Adjustable 3.3W LED MR-16 Remote Head / Black Housing
INDRHLED162B	9.63"L x 5.5"H x 4.88"Dp / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / Black Housing

Change "B" to "W" or "G" for white or gray housing. Add "TP" for tamper-proof.

## LED Hazardous Location Remote Head

Ideal for areas that use chemicals that create a hazardous environment. Rated for class 1, division 2, groups A, B, C, & D.



ITEM NO.	DESCRIPTION
HLRHLED161G	9.63"L x 5.5"H x 4.88"Dp / 1 Fully Adjustable 3.3W LED MR-16 Remote Head / Gray Housing
HLRHLED162G	9.63"L x 5.5"H x 4.88"Dp / 2 Fully Adjustable 3.3W LED MR-16 Remote Heads / Gray Housing

Add "TP" for tamper-proof.

# INVERTERS



## Micro Emergency Power System

ITEM NO.	DESCRIPTION
MPS-32	14.75"L x 3.13"W x 7.38"H / 32W 32VA For 1.5 Hours / Lead-Calc Battery / Weight 14 lbs.
MPS-55	14.75"L x 4.38"W x 7.38"H / 55W 55VA For 1.5 Hours / Lead-Calc Battery / Weight 18 lbs.
MPS-20	14.75"L x 3.13"W x 7.38"H / 20W 20VA For 1.5 Hours / NiCad Battery / Weight 11 lbs.
MPS-35	14.75"L x 4.38"W x 7.38"H / 35W 35VA For 1.5 Hours / NiCad Battery / Weight 12 lbs.

ITEM NO.	DESCRIPTION
<b>SPS Accessories</b>	
-S	Surface Mount Housing
-R	Recess Mount Housing
-T	Plenum Rated Ceiling T-Grid Mount Housing
-RTS	Remote Test Switch Panel
-SDT	Self-Testing / Self-Diagnostics
-CEC	Title 20 Compliant

Consult for special housing color options.




## Mini Emergency Power System

ITEM NO.	DESCRIPTION
SPS-55/125	16.75"L x 4.38"W x 11.75"H / 55W 125VA For 1.5 Hours / Lead-Calc Battery / Weight 30 lbs.
SPS-110/125	16.75"L x 4.38"W x 11.75"H / 110W 125VA For 1.5 Hours / Lead-Calc Battery / Weight 42 lbs.
SPS110/250	16.75"L x 6.38"W x 11.75"H / 110W 250VA For 1.5 Hours / Lead-Calc Battery / Weight 45.2 lbs.
SPS220/250	16.75"L x 6.38"W x 11.75"H / 220W 250VA For 1.5 Hours / Lead-Calc Battery / Weight 60 lbs.

ITEM NO.	DESCRIPTION
<b>SPS Accessories</b>	
-S	Surface Mount Housing
-R	Recess Mount Housing
-T	Plenum Rated Ceiling T-Grid Mount Housing
-RTS	Remote Test Switch Panel
-SDT	Self-Testing / Self-Diagnostics
-CEC	Title 20 Compliant
-AO	Adjustable Output/Dimmer Bypass
-4C	4 Output Circuit Switching

Consult for special housing color options.

# INVERTERS



LPS-375W



LPS-600W

## Large Emergency Power System

ITEM NO.	DESCRIPTION
LPS-375W	18.0"L x 8.25"W x 16.63"H / 375W 375VA For 1.5 Hours / Lead-Calc Battery / Weight 113 lbs.
LPS-600W	18.0"L x 8.25"W x 25.25"H / 600W 600VA For 1.5 Hours / Lead-Calc Battery / Weight 172 lbs.

ITEM NO.	DESCRIPTION
<b>SPS Accessories</b>	
-OCB1	One Output Breaker
-OCB2	Two Output Breaker
-ICB	Input Breaker
-4AO	Adjustable Output/Dimmer Bypass
-4C	Four Output Circuit Switching
-SDT	Self-Testing / Self-Diagnostics

Consult for special housing color options.

# EZLED

The Benefits of LED with Ease,  
Practicality, and Flexibility



## THE SIMPLE LED SOLUTION

The most economical, user friendly series of LED fixtures with energy savings, quality of light, long life, and hassle-free maintenance. EZLED fixtures are UL listed with the latest LED T8 and T5 bypass lamps. These fixtures provide flexibility to change the wattage and color temperature at any time, and are less expensive than comparable fluorescent fixtures. Concerned about maintenance with an LED array and driver fixture? EZLED resolves that issue by utilizing self-contained, LED lamps that fit directly into the fixture just like a fluorescent lamp. Fixture performance will evolve over time with the evolution of the LED lamp technology, and our five-year warranty guarantees a reliable, high quality product.



*All of our EZLED fixtures can be sold  
“LED Ready” without tubes!*

Mobern uses top quality **Savegreen** LED T8 and T5 lamps that are field tested for demanding applications.



For Emergency Option, see  
page 103.

### Troffer

ITEM NO.	DESCRIPTION
RG-14232LEDL15W840	1x4 / 47.88"L x 12.0"W x 3.75"H / Two 15W 1,740L LED T8 Lamps / A12 .100 Thick Lens Standard / 4000K
RG-22217LEDL9W840	2x2 / 23.75"L x 23.75"W x 3.75"H / Two 9W 1,050L LED T8 Lamps / A12 .100 Thick Lens Standard / 4000K
RG-22317LEDL9W840	2x2 / 23.75"L x 23.75"W x 3.75"H / Three 9W 1,050L LED T8 Lamps / A12 .100 Thick Lens Standard / 4000K
RG-22417LEDL9W840	2x2 / 23.75"L x 23.75"W x 3.75"H / Four 9W 1,050L LED T8 Lamps / A12 .100 Thick Lens Standard / 4000K
RG-24232LEDL15W840	2x4 / 47.75"L x 23.75"W x 3.75"H / Two 15W 1,740L LED T8 Lamps / A12 .100 Thick Lens Standard / 4000K
RG-24332LEDL15W840	2x4 / 47.75"L x 23.75"W x 3.75"H / Three 15W 1,740L LED T8 Lamps / A12 .100 Thick Lens Standard / 4000K
RG-24432LEDL15W840	2x4 / 47.75"L x 23.75"W x 3.75"H / Four 15W 1,740L LED T8 Lamps / A12 .100 Thick Lens Standard / 4000K

Add "SSM" for integrated microwave sensor. Also available in 30K, 40K, & 50K.





Frame-in-kits available for recessed fixtures to mount in hard ceilings:

- ▶ M596A 1x4
- ▶ M565A 2x2
- ▶ M566A 2x4

## Parabolic

ITEM NO.	DESCRIPTION
RP-14232LED8L15W840	1x4 / 47.75"L x 11.75"W x 5.5"H / Two 15W 1,740L LED T8 Lamps / 8 Cell Louver / 4000K
RP-22217LED9L9W840	2x2 / 23.75"L x 23.75"W x 5.5"H / Two 9W 1,050L LED T8 Lamps / 9 Cell Louver / 4000K
RP-22317LED9L9W840	2x2 / 23.75"L x 23.75"W x 5.5"H / Three 9W 1,050L LED T8 Lamps / 9 Cell Louver / 4000K
RP-22417LED9L9W840	2x2 / 23.75"L x 23.75"W x 5.5"H / Four 9W 1,050L LED T8 Lamps / 9 Cell Louver / 4000K
RP-24232LED12L15W840	2x4 / 47.75"L x 23.75"W x 5.5"H / Two 15W 1,740L LED T8 Lamps / 12 Cell Louver / 4000K
RP-24232LED18L15W840	2x4 / 47.75"L x 23.75"W x 5.5"H / Two 15W 1,740L LED T8 Lamps / 18 Cell Louver / 4000K
RP-24332LED18L15W840	2x4 / 47.75"L x 23.75"W x 5.5"H / Three 15W 1,740L LED T8 Lamps / 18 Cell Louver / 4000K
RP-24432LED18L15W840	2x4 / 47.75"L x 23.75"W x 5.5"H / Four 15W 1,740L LED T8 Lamps / 18 Cell Louver / 4000K
RP-24432LED32L15W840	2x4 / 47.75"L x 23.75"W x 5.5"H / Four 15W 1,740L LED T8 Lamps / 32 Cell Louver / 4000K

Add "SSM" for integrated microwave sensor. Also available in 30K, 35K & 50K.

## Center Basket

ITEM NO.	DESCRIPTION
RDIS-14232LEDPFL15W840	1x4 / 47.0"L x 12.0"W x 3.26"H / Two 15W 1,740L LED T8 Lamps / Perforated Basket / 4000K
RDIS-22217LEDPFL9W840	2x2 / 24.0"L x 24.0"W x 3.26"H / Two 9W 1,050L LED T8 Lamps / Perforated Basket / 4000K
RDIS-22317LEDPFL9W840	2x2 / 24.0"L x 24.0"W x 3.26"H / Three 9W 1,050L LED T8 Lamps / Perforated Basket / 4000K
RDIS-24232LEDPFL15W840	2x4 / 47.0"L x 24.0"W x 3.26"H / Two 15W 1,740L LED T8 Lamps / Perforated Basket / 4000K
RDIS-24332LEDPFL15W840	2x4 / 47.0"L x 24.0"W x 3.26"H / Three 15W 1,740L LED T8 Lamps / Perforated Basket / 4000K

Add "INV5" for integrated inverter. Add "SSM" for integrated microwave sensor. Change "PF" to "FR" for frosted lens. Also available in 30K, 35K & 50K.

## Dual Basket

ITEM NO.	DESCRIPTION
RDISD-22217LEDPFL9W840	2x2 / 23.68"L x 23.68"W x 3.25"H / Two 9W 1,050L LED T8 Lamps / Perforated Baskets / 4000K
RDISD-24232LEDPFL15W840	2x4 / 47.67"L x 23.68"W x 3.25"H / Two 15W 1,740L LED T8 Lamps / Perforated Baskets / 4000K

Change "PF" to "RL" for ribbed linear lens. Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.



Special red sockets identify fixtures made for LED T8 lamps!





## Deep Center Basket

ITEM NO.	DESCRIPTION
RDICB-22217LEDL9W840	2x2 / 24.0"L x 23.82"W x 5.5"H / Two 9W 1,050L LED T8 Lamps / White Opal Acrylic Lens Standard / 4000K
RDICB-22317LEDL9W840	2x2 / 24.0"L x 23.82"W x 5.5"H / Three 9W 1,050L LED T8 Lamps / White Opal Acrylic Lens Standard / 4000K
RDICB-24232LEDL15W840	2x4 / 48.0"L x 23.82"W x 5.5"H / Two 15W 1,740L LED T8 Lamps / White Opal Acrylic Lens Standard / 4000K
RDICB-24332LEDL15W840	2x4 / 48.0"L x 23.82"W x 5.5"H / Three 15W 1,740L LED T8 Lamps / White Opal Acrylic Lens Standard / 4000K

Add "INV5" for integrated inverter.. Also available in 30K, 35K & 50K.



## 4"x 4" Recessed Linear (For T-Bar Ceiling)

ITEM NO.	DESCRIPTION
L44-R117LEDWHSFL9W840	24"L x 4"W x 4"H / One 9W 1,050L LED T8 Lamp / White Finish / Frosted Lens / 4000K
L44-R217LEDWHSFL9W840	24"L x 4"W x 4"H / Two 9W 1,050L LED T8 Lamps / White Finish / Frosted Lens / 4000K
L44-R132LEDWHSFL15W840	48"L x 4"W x 4"H / One 15W 1,740L LED T8 Lamp / White Finish / Frosted Lens / 4000K
L44-R232LEDWHSFL15W840	48"L x 4"W x 4"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K
L44-R132TANLEDWHSFL15W840	96"L x 4"W x 4"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K
L44-R232TANLEDWHSFL15W840	96"L x 4"W x 4"H / Four 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

Change "SF" to "MW" (matte white), "S5" (specular parabolic), "LV" (baffled louver), or "A" (prismatic acrylic) for lens options. Consult for other finish options. Add "INV5" for integrated inverter.. Also available in 30K, 35K & 50K.

**Also Available:**

- ▶ **L44RF** (Recessed Flange)
- ▶ **L44RRXX** (Recessed Flangeless)
- XX - Sheetrock Depth



## 6"x 6" Recessed Linear (For T-Bar Ceilings)

ITEM NO.	DESCRIPTION
L66-R117LEDWHMWL9W840	26.0"L x 5.75"W x 6.0"H / One 9W 1,050L LED T8 Lamp / White Finish / Matte White Lens / 4000K
L66-R217LEDWHMWL9W840	26.0"L x 5.75"W x 6.0"H / Two 9W 1,050L LED T8 Lamps / White Finish / Matte White Lens / 4000K
L66-R132LEDWHMWL15W840	47.94"L x 5.75"W x 6.0"H / One 15W 1,740L LED T8 Lamp / White Finish / Matte White Lens / 4000K
L66-R232LEDWHMWL15W840	47.94"L x 5.75"W x 6.0"H / Two 15W 1,740L LED T8 Lamps / White Finish / Matte White Lens / 4000K
L66-R132TANLEDWHMWL15W840	95.94"L x 5.75"W x 6.0"H / Two 15W 1,740L LED T8 Lamps / White Finish / Matte White Lens / 4000K
L66-R232TANLEDWHMWL15W840	95.94"L x 5.75"W x 6.0"H / Four 15W 1,740L LED T8 Lamps / White Finish / Matte White Lens / 4000K

Change "SF" to "MW" (matte white), "S5" (specular parabolic), "LV" (baffled louver), or "A" (prismatic acrylic) for lens options. Add "INV5" for integrated inverter.. Also available in 30K, 35K & 50K.

**Also Available:**

- ▶ **L66RF** (Recessed Flange)
- ▶ **L66RRXX** (Recessed Flangeless)
- XX - Sheetrock Depth



L66RF

## 2.5" Recessed Linear (Flanged For Hard Ceilings)



ITEM NO.	DESCRIPTION
LD23-RF117LEDWHSFL9W840	23.60"L x 2.38"W x 3.35"H / One 9W 1,050L LED T8 Lamp / White Finish / Frosted Lens / 4000K
LD23-RF132LEDWHSFL15W840	47.32"L x 2.38"W x 3.35"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K
LD23-RF132TANLEDWHSFL15W840	96.0"L x 2.38"W x 3.35"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

Add "INV5" for integrated inverter. Change "WH" to "BK", "IR", "SL" or "BZ" for black, iron, silver, or bronze finish. Also available in 30K, 35K & 50K.

## Louver Blade Linear Pendant



ITEM NO.	DESCRIPTION
LPLI-232LEDWHH4W5L15W840	48.0"L x 10.8"W x 3.5"H / Two 15W 1,740L LED T8 Lamps / White Finish / Baffled Louver / 4000K
LPLI-232TANLEDWHH4W5L15W840	96.0"L x 10.8"W x 3.5"H / Four 15W 1,740L LED T8 Lamps / White Finish / Baffled Louver / 4000K

Consult for other finish options. Add "INV5" for integrated inverter.. Also available in 30K, 35K & 50K.

## 4"x 4" Linear Pendant



ITEM NO.	DESCRIPTION
L44-P117LEDWHSFH4W5L9W840	24"L x 4"W x 4"H / One 9W 1,050L LED T8 Lamp / White Finish / Frosted Lens / 4000K
L44-P217LEDWHSFH4W5L9W840	24"L x 4"W x 4"H / Two 9W 1,050L LED T8 Lamps / White Finish / Frosted Lens / 4000K
L44-P132LEDWHSFH4W5L15W840	48"L x 4"W x 4"H / One 15W 1,740L LED T8 Lamp / White Finish / Frosted Lens / 4000K
L44-P232LEDWHSFH4W5L15W840	48"L x 4"W x 4"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K
L44-P132TANLEDWHSFH4W5L15W840	96"L x 4"W x 4"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K
L44-P232TANLEDWHSFH4W5L15W840	96"L x 4"W x 4"H / Four 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

Change "SF" to "MW" (matte white), "S5" (specular parabolic), "LV" (baffled louver), or "A" (prismatic acrylic) for lens options. Consult for other finish options. Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## 6"x 6" Linear Pendant



ITEM NO.	DESCRIPTION
L66-P117LEDWHMWL9W840H4W5	26.0"L x 5.75"W x 6.0"H / One 9W 1,050L LED T8 Lamp / White Finish / Matte White Lens / 4000K
L66-P217LEDWHMWL9W840H4W5	26.0"L x 5.75"W x 6.0"H / Two 9W 1,050L LED T8 Lamps / White Finish / Matte White Lens / 4000K
L66-P132LEDWHMWL15W840H4W5	47.94"L x 5.75"W x 6.0"H / One 15W 1,740L LED T8 Lamp / White Finish / Matte White Lens / 4000K
L66-P232LEDWHMWL15W840H4W5	47.94"L x 5.75"W x 6.0"H / Two 15W 1,740L LED T8 Lamps / White Finish / Matte White Lens / 4000K
L66-P132TANLEDWHMWL15W840H4W5	95.94"L x 5.75"W x 6.0"H / Two 15W 1,740L LED T8 Lamps / White Finish / Matte White Lens / 4000K
L66-P232TANLEDWHMWL15W840H4W5	95.94"L x 5.75"W x 6.0"H / Four 15W 1,740L LED T8 Lamps / White Finish / Matte White Lens / 4000K

Change "SF" to "MW" (matte white), "S5" (specular parabolic), "LV" (baffled louver), or "A" (prismatic acrylic) for lens options. Consult for other finish options. Add "INV5" for integrated inverter.. Also available in 30K, 35K & 50K.



### LED T8 Pendant

#### ITEM NO.

#### DESCRIPTION

LTP-132LEDCHL15W840	48.45"L x 1.75"W x 2.38"H / One 15W 1,740L LED T8 Lamp / Chrome Finish / 4000K
LTP-132LEDWHL15W840	48.45"L x 1.75"W x 2.38"H / One 15W 1,740L LED T8 Lamp / White Finish / 4000K

Also available in 30K, 35K & 50K.



*Optional Chrome Finish.*

### 1 Light 2.5" Enclosed

#### ITEM NO.

#### DESCRIPTION

LD23-132LEDFRH4W5L15W840	47.32"L x 2.38"W x 3.35"H / One 15W 1,740L LED T8 Lamp / Frosted Lens / 4000K
LD23-132TANLEDFRH4W5L15W840	96.0"L x 2.38"W x 3.35"H / Two 15W 1,740L LED T8 Lamps / Frosted Lens / 4000K

Add "INV5" for integrated inverter. Change "WH" to "BK", "IR", "SL" or "BZ" for black, iron, silver, or bronze finish. Also available in 30K, 35K & 50K.



### Louvered 6" Decorative Linear

#### ITEM NO.

#### DESCRIPTION

DLV6-232LEDWHH4W5L15W840	48.0"L x 6.0"W x 5.25"H / Two 15W 1,740L LED T8 Lamps / White Finish / 4000K
DLV6-232TANLEDWHH4W5L15W840	96.0"L x 6.0"W x 5.25"H / Four 15W 1,740L LED T8 Lamps / White Finish / 4000K

Add "INV5" for integrated inverter.. Also available in 30K, 35K & 50K.







## Surface Troffer

ITEM NO.	DESCRIPTION
SRG-14232LEDL15W840	1x4 / 47.75"L x 12.0"W x 3.75"H / Two 15W 1,740L LED T8 Lamps / 4000K
SRG-22217LEDL9W840	2x2 / 23.75"L x 23.75"W x 3.75"H / Two 9W 1,050L LED T8 Lamps / 4000K
SRG-22317LEDL9W840	2x2 / 23.75"L x 23.75"W x 3.75"H / Three 9W 1,050L LED T8 Lamps / 4000K
SRG-22417LEDL9W840	2x2 / 23.75"L x 23.75"W x 3.75"H / Four 9W 1,050L LED T8 Lamps / 4000K
SRG-24232LEDL15W840	2x4 / 47.75"L x 23.75"W x 3.75"H / Two 15W 1,740L LED T8 Lamps / 4000K
SRG-24332LEDL15W840	2x4 / 47.75"L x 23.75"W x 3.75"H / Three 15W 1,740L LED T8 Lamps / 4000K
SRG-24432LEDL15W840	2x4 / 47.75"L x 23.75"W x 3.75"H / Four 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Add "SSM" for integrated microwave sensor. See page 57 for lens, door, & gasketing options. Also available in 30K, 35K & 50K.

## Surface Parabolic

ITEM NO.	DESCRIPTION
SPR-14232LED8L15W840	1x4 / 48.0"L x 12.0"W x 5.5"H / Two 15W 1,740L LED T8 Lamps / 8 Cell Louver / 4000K
SPR-22217LED9L15W840	2x2 / 24.0"L x 24.0"W x 5.5"H / Two 9W 1,050L LED T8 Lamps / 9 Cell Louver / 4000K
SPR-22317LED9L15W840	2x2 / 24.0"L x 24.0"W x 5.5"H / Three 9W 1,050L LED T8 Lamps / 9 Cell Louver / 4000K
SPR-22417LED9L15W840	2x2 / 24.0"L x 24.0"W x 5.5"H / Four 9W 1,050L LED T8 Lamps / 9 Cell Louver / 4000K
SPR-24232LED12L15W840	2x4 / 48.0"L x 24.0"W x 5.5"H / Two 15W 1,740L LED T8 Lamps / 12 Cell Louver / 4000K
SPR-24232LED18L15W840	2x4 / 48.0"L x 24.0"W x 5.5"H / Two 15W 1,740L LED T8 Lamps / 18 Cell Louver / 4000K
SPR-24332LED18L15W840	2x4 / 48.0"L x 24.0"W x 5.5"H / Three 15W 1,740L LED T8 Lamps / 18 Cell Louver / 4000K
SPR-24432LED18L15W840	2x4 / 48.0"L x 24.0"W x 5.5"H / Four 15W 1,740L LED T8 Lamps / 18 Cell Louver / 4000K
SPR-24432LED32L15W840	2x4 / 48.0"L x 24.0"W x 5.5"H / Four 15W 1,740L LED T8 Lamps / 32 Cell Louver / 4000K

Add "INV5" for integrated inverter. Add "SSM" for integrated microwave sensor. Add "OL" for overly lens. Also available in 30K, 35K & 50K.



## Surface Center Basket

ITEM NO.	DESCRIPTION
SRDIS-14132LEDPFL15W840	1x4 / 47.8"L x 11.7"W x 3.25"H / One 15W 1,740L LED T8 Lamp / Perforated Basket / 4000K
SRDIS-22217LEDPFL9W840	2x2 / 24.0"L x 24.0"W x 3.25"H / Two 9W 1,050L LED T8 Lamps / Perforated Basket / 4000K
SRDIS-22317LEDPFL9W840	2x2 / 24.0"L x 24.0"W x 3.25"H / Three 9W 1,050L LED T8 Lamps / Perforated Basket / 4000K
SRDIS-24232LEDPFL15W840	2x4 / 48.0"L x 24.0"W x 3.25"H / Two 15W 1,740L LED T8 Lamps / Perforated Basket / 4000K
SRDIS-24332LEDPFL15W840	2x4 / 48.0"L x 24.0"W x 3.25"H / Three 15W 1,740L LED T8 Lamps / Perforated Basket / 4000K

Add "INV5" for integrated inverter. Add "SSM" for integrated microwave sensor. Change "PF" to "RL" or "FR" for ribbed linear or frosted lens. Also available in 30K, 35K & 50K.





## Surface Dual Basket

ITEM NO.	DESCRIPTION
SRDISD-22217LEDPFL9W840	2x2 / 24.0"L x 24.0"W x 3.25"H / Two 9W 1,050L LED T8 Lamps / Perforated Basket / 4000K
SRDISD-24232LEDPFL15W840	2x4 / 48.0"L x 24.0"W x 3.25"H / Two 15W 1,740L LED T8 Lamps / Perforated Basket / 4000K

Add "INV5" for integrated inverter. Change "PF" to "RL" for ribbed linear lens. Also available in 30K, 35K & 50K.

## Eclipse



ITEM NO.	DESCRIPTION
MCH-217LEDWHL9W840	25.75"L x 9.5"W x 4.5"H / Two 9W 1,050L LED T8 Lamps / White Finish / 4000K
MCH-232LEDWHL15W840	51.25"L x 9.5"W x 4.5"H / Two 15W 1,740L LED T8 Lamps / White Finish / 4000K
MCH-417LEDWHL9W840	25.75"L x 16.5"W x 4.5"H / Four 9W 1,050L LED T8 Lamps / White Finish / 4000K
MCH-432LEDWHL15W840	51.25"L x 16.5"W x 4.5"H / Four 15W 1,740L LED T8 Lamps / White Finish / 4000K

Add "INV5" for integrated inverter. See end cap options on page 39. Also available in 30K, 35K & 50K.

## Cloud Surface Linear



ITEM NO.	DESCRIPTION
9-232LEDL15W840	50.5"L x 11.75"W / Two 15W 1,740L LED T8 Lamps / 4000K
15-417LEDL9W840	26.5"L x 17.0"W / Four 9W 1,050L LED T8 Lamps / 4000K
15-432LEDL15W840	50.5"L x 17.0"W / Four 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## Crown



ITEM NO.	DESCRIPTION
CWN-22217LEDWHMWL9W840	2x2 / 25.0"L x 25.0"W x 4.13"H / Two 9W 1,050L LED T8 Lamps / White Finish / Matte White Lens / 4000K
CWN-22417LEDWHMWL9W840	2x2 / 25.0"L x 25.0"W x 4.13"H / Four 9W 1,050L LED T8 Lamps / White Finish / Matte White Lens / 4000K
CWN-14232LEDWHMWL15W840	1x4 / 48.88"L x 11.5"W x 4.13"H / Two 15W 1,740L LED T8 Lamps / White Finish / Matte White Lens / 4000K
CWN-24432LEDWHMWL15W840	2x4 / 48.88"L x 16.75"W x 4.13"H / Four 15W 1,740L LED T8 Lamps / White Finish / Matte White Lens / 4000K

Add "INV5" for integrated inverter. Change "WH" to "GO" or "BW" for golden oak or bleached white finish (special order). Also available in 30K, 35K & 50K.

## Wraparound 7"



ITEM NO.	DESCRIPTION
769-217LEDL9W840	24.0"L x 7.63"W x 3.0"H / Two 9W 1,050L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K
769-232LEDL15W840	48.0"L x 7.63"W x 3.0"H / Two 15W 1,740L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K
769-332LEDL15W840	48.0"L x 13.0"W x 3.0"H / Three 15W 1,740L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K
769-432LEDL15W840	48.0"L x 13.0"W x 3.0"H / Four 15W 1,740L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K

Add "INV5" for integrated inverter. Add "FR" after "LED" for frosted lens. Also available in 30K, 35K & 50K.

# EZLED

## Wraparound 9"



ITEM NO.	DESCRIPTION
770-232LEDL15W840	48.0"L x 9.38"W x 3.1"H / Two 15W 1,740L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## Specification Grade Wraparound



ITEM NO.	DESCRIPTION
772-217LEDL9W840	24.0"L x 11.25"W x 3.4"H / Two 9W 1,050L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K
772-232LEDL15W840	48.0"L x 11.25"W x 3.4"H / Two 15W 1,740L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K
772-232TANLEDL15W840	96.0"L x 15.8"W x 3.4"H / Four 15W 1,740L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K
772-432LEDL15W840	48.0"L x 15.8"W x 3.4"H / Four 15W 1,740L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K
772-432TANLEDL15W840	96.0"L x 15.8"W x 3.4"H / Eight 15W 1,740L LED T8 Lamps / Clear Prismatic Lens Standard / 4000K

Add "INV5" for integrated inverter. Add "A69" for wireguard per 4ft. Also available in 30K, 35K & 50K.

## Narrow Wraparound



ITEM NO.	DESCRIPTION
772N-117LEDL15W840	24.0"L x 5.63"W x 3.19"H / One 9W 1,050L LED T8 Lamp / Clear Lens Standard / 4000K
772N-132LEDL15W840	48.0"L x 5.63"W x 3.19"H / Two 15W 1,740L LED T8 Lamps / Clear Lens Standard / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## Corridor Linear



ITEM NO.	DESCRIPTION
15-117LEDL9W840	24.0"L x 4.62"W x 4.5"H / One 9W 1,050L LED T8 Lamp / White Opal Acrylic Lens Standard / 4000K
15-132LEDL15W840	48.0"L x 4.62"W x 4.5"H / One 15W 1,740L LED T8 Lamp / White Opal Acrylic Lens Standard / 4000K
15-132TANLEDL15W840	96.0"L x 4.62"W x 4.5"H / Two 15W 1,740L LED T8 Lamps / White Opal Acrylic Lens Standard / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## 4.25" 2 Or 3 Light Strip



ITEM NO.	DESCRIPTION
44-217LEDL9W840	24.0"L x 4.25"W x 2.0"H / Two 9W 1,050L LED T8 Lamps / 4000K
44-317LEDL9W840	24.0"L x 8.75"W x 2.0"H / Three 9W 1,050L LED T8 Lamps / 4000K
44-232LEDL15W840	48.0"L x 4.25"W x 2.0"H / Two 15W 1,740L LED T8 Lamps / 4000K
44-332LEDL15W840	48.0"L x 8.75"W x 2.0"H / Three 15W 1,740L LED T8 Lamps / 4000K
44-232TANLEDL15W840	96.0"L x 4.25"W x 2.0"H / Four 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## 2.75" 1 Light Strip



ITEM NO.	DESCRIPTION
42-117LEDL9W840	24.0"L x 2.75"W x 1.8"H / One 9W 1,050L LED T8 Lamp / 4000K
42-132LEDL15W840	48.0"L x 2.75"W x 1.8"H / One 15W 1,740L LED T8 Lamp / 4000K
42-132TANLEDL15W840	96.0"L x 2.75"W x 1.8"H / Two 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## 1 Light Micro Strip

ITEM NO.	DESCRIPTION
ZMS-132LEDL15W840	49.5"L x 1.38"W x 1.69"H / One 15W 1,740L LED T8 Lamp / 4000K

Also available in 30K, 35K & 50K.

## Side Mount Strip



Order A69 for wire guard.

ITEM NO.	DESCRIPTION
42SC-117LEDL9W840	24.0"L x 2.75"W x 2.0"H / One 9W 1,050L LED T8 Lamp / 4000K
42SC-217LEDL9W840	24.0"L x 2.75"W x 2.0"H / Two 9W 1,050L LED T8 Lamps / 4000K
42SC-132LEDL15W840	48.0"L x 2.75"W x 2.0"H / One 15W 1,740L LED T8 Lamps / 4000K
42SC-232LEDL15W840	48.0"L x 2.75"W x 2.0"H / Two 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## Industrial Strip

ITEM NO.	DESCRIPTION
1-232LEDL15W840	48.0"L x 10.25"W x 4.2"H / Two 15W 1,740L LED T8 Lamps / 4000K
1-332LEDL15W840	48.0"L x 10.25"W x 4.2"H / Three 15W 1,740L LED T8 Lamps / 4000K
1-232TANLEDL15W840	96.0"L x 10.25"W x 4.2"H / Four 15W 1,740L LED T8 Lamps / 4000K
1-332TANLEDL15W840	96.0"L x 10.25"W x 4.2"H / Six 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## Recessed Strip



ITEM NO.	DESCRIPTION
RCS-132LEDL15W840	47.96"L x 11.71"W x 5.45"H / One 15W 1,740L LED T8 Lamp / 4000K
RCS-232LEDL15W840	47.96"L x 11.71"W x 5.45"H / Two 15W 1,740L LED T8 Lamps / 4000K
RCS-132TANLEDL15W840	95.92"L x 11.71"W x 5.45"H / Two 15W 1,740L LED T8 Lamps / 4000K
RCS-232TANLEDL15W840	95.92"L x 11.71"W x 5.45"H / Four 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.





## Premium High Bay

ITEM NO.	DESCRIPTION
FHBC-432LEDL15W850	48.1"L x 11.4"W x 3.6"H / Four 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBC-632LEDL15W850	48.1"L x 16.4"W x 3.6"H / Six 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBC-832LEDL15W850	48.1"L x 16.4"W x 3.6"H / Eight 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBC-1032LEDL15W850	48.1"L x 20.4"W x 3.6"H / Ten 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBC-1232LEDL15W850	48.1"L x 20.4"W x 3.6"H / Twelve 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K

Add "INV5" for integrated inverter. Add "WG" for wire guard. Add "OS" for occupancy sensor. Also available in 30K, 35K & 40K.

## Industrial Galvanized High Bay

ITEM NO.	DESCRIPTION
FHBI-432LEDL15W850	48.0"L x 14.25"W x 3.25"H / Four 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBI-632LEDL15W850	48.0"L x 21.25"W x 3.25"H / Six 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBI-832LEDL15W850	48.0"L x 28.25"W x 3.25"H / Eight 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBI-1032LEDL15W850	48.0"L x 35.3"W x 3.25"H / Ten 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBI-1232LEDL15W850	48.0"L x 42.25"W x 3.25"H / Twelve 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K

Add "INV5" for integrated inverter. Add "WG" for wire guard. Add "OS" for occupancy sensor. Also available in 30K, 35K & 40K.

## High Bay Workhorse

ITEM NO.	DESCRIPTION
FHBF-432TANLEDL15W850	96.0"L x 15.8"W x 3.4"H / Eight 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBF-432LEDL15W850	48.0"L x 15.8"W x 3.4"H / Four 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBF-632TANLEDL15W850	96.0"L x 15.8"W x 3.4"H / Six 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K
FHBF-632LEDL15W850	48.0"L x 15.8"W x 3.4"H / Six 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K

Add "INV5" for integrated inverter. Add "WG" for wire guard. Add "OS" for occupancy sensor. Also available in 30K, 35K & 40K.



ITEM NO.	DESCRIPTION
<b>FHBF Accessories</b>	
A-FHBFWG	Wire Guard 4 Or 6 Light Galvanized
A-FHBFWG-WH	Wire Guard 4 Or 6 Light White
A144-XX	Tong Hanger / End Mount Pair (Pair) With Footage Of Chain / XX = Length Of Chain
AC120-TOGGLE-2PK	Y-Hook-10' Cable Mounting Kit & 2 Spring Clips

ITEM NO.	DESCRIPTION
<b>FHBF Lens Accessories</b>	
L-FHBFCLLEN	Clear Lens .100
L-FHBF125LEN	Clear Lens .125
L-FHBFALLEN	Acrylic Lens .100
L-FHBFPCLEN	Polycarbonate Lens



## Narrow High Bay Workhorse

ITEM NO.	DESCRIPTION
FHBFN-132LEDL15W850	48.0"L x 7.0"W x 3.4"H / One 15W 1,740L LED T8 Lamp / Full Specular Mirror Wide Reflector Standard / 5000K
FHBFN-232LEDL15W850	48.0"L x 7.0"W x 3.4"H / Two 15W 1,740L LED T8 Lamps / Full Specular Mirror Wide Reflector Standard / 5000K

Add "INV5" for integrated inverter. Add "OS" for occupancy sensor. Also available in 30K, 35K & 40K.

## Baffled High Bay

ITEM NO.	DESCRIPTION
FHBR-232LEDL15W850	48.0"L x 11.25"W x 4.25"H / Two 15W 1,740L LED T8 Lamps / White Reflector Standard / 5000K
FHBR-332LEDL15W850	48.0"L x 11.25"W x 4.25"H / Three 15W 1,740L LED T8 Lamps / White Reflector Standard / 5000K
FHBR-432LEDL15W850	48.0"L x 11.25"W x 4.25"H / Four 15W 1,740L LED T8 Lamps / White Reflector Standard / 5000K
FHBR232TANLEDL15W850	96.0"L x 11.25"W x 4.25"H / Four 15W 1,740L LED T8 Lamps / White Reflector Standard / 5000K
FHBR332TANLEDL15W850	96.0"L x 11.25"W x 4.25"H / Six 15W 1,740L LED T8 Lamps / White Reflector Standard / 5000K
FHBR432TANLEDL15W850	96.0"L x 11.25"W x 4.25"H / Eight 15W 1,740L LED T8 Lamps / White Reflector Standard / 5000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 40K.



## Wet Location Vapor Tight High Bay



ITEM NO.	DESCRIPTION
VWFHB-432LEDCLL15W850	51.91"L x 14.61"W x 5.95"H / Four 15W 1,740L LED T8 Lamps / Clear Acrylic Lens / 5000K
VWFHB-632LEDCLL15W850	51.91"L x 14.61"W x 5.95"H / Six 15W 1,740L LED T8 Lamps / Clear Acrylic Lens / 5000K

Add "INV5" for integrated inverter. Add "OS" for occupancy sensor. Also available in 30K, 35K & 40K.

## Citadel Enclosure



ITEM NO.	DESCRIPTION
VW-232LEDSSCL15W840	51.85"L x 8.77"W x 4.27"H / Two 15W 1,740L LED T8 Lamps / Shallow Smooth Clear Lens / 4000K
VW-332LEDSSCL15W840	51.85"L x 8.77"W x 4.27"H / Three 15W 1,740L LED T8 Lamps / Shallow Smooth Clear Lens / 4000K
VW-232TANLEDRCCL15W840	100.00"L x 8.77"W x 4.38"H / Four 15W 1,740L LED T8 Lamps / Ribbed Clear Lens / 4000K

Add "INV5" for integrated inverter. See lens options on page 65. Add "OS" for occupancy sensor. Also available in 30K, 35K & 50K.



## Ballast Cover Retrofit Kit (Ideal To Change 8ft. Lamps To 4ft. Tandem)



ITEM NO.	DESCRIPTION
RKBC-42132LEDWRL15W840	48.0"L x 4.25"W x 0.5"H / One 15W 1,740L LED T8 Lamp / 4000K
RKBC-42232LEDWRL15W840	48.0"L x 4.25"W x 0.5"H / Two 15W 1,740L LED T8 Lamps / 4000K
RKBC-50132LEDWRL15W840	48.0"L x 5.0"W x 0.5"H / One 15W 1,740L LED T8 Lamp / 4000K
RKBC-50232LEDWRL15W840	48.0"L x 5.0"W x 0.5"H / Two 15W 1,740L LED T8 Lamps / 4000K
RKBC-42132TANLEDWRL15W840	96.0"L x 4.25"W x 0.5"H / Two 15W 1,740L LED T8 Lamps / 4000K
RKBC-42232TANLEDWRL15W840	96.0"L x 4.25"W x 0.5"H / Four 15W 1,740L LED T8 Lamps / 4000K
RKBC-50132TANLEDWRL15W840	96.0"L x 5.0"W x 0.5"H / Two 15W 1,740L LED T8 Lamps / 4000K
RKBC-50232TANLEDWRL15W840	96.0"L x 5.0"W x 0.5"H / Four 15W 1,740L LED T8 Lamps / 4000K

Also available in 30K, 35K & 50K.

## How To Add Emergency To **EZLED**



### KT-EMRG-LED-5-500-AC CONSTANT WATTAGE LED EMERGENCY BACK-UP

LED Emergency Back-Up Driver | Standard Side Exit Wire Leads | 5W Output

DRIVER TYPE: Constant Wattage LED Emergency

MAX. OUTPUT POWER: 5W

INPUT VOLTAGE: 120-277VAC ± 10%

OUTPUT VOLTAGE: 40-300Vdc

OUTPUT CURRENT: Load Dependant

WARRANTY: 5 YEARS


PRODUCT FEATURES

- Optimized for Keystone single ended direct drive LED tubes. Contact Keystone for details on functioning with other Type B LED tubes
- Illuminates entire LED load at reduced output under emergency mode
- One piece design with metal housing
- 2-in-1 LED test switch and indicator light included
- Evaluated to UL 924 requirements

To order, add "INV5" to the end of **EZLED** part number.



## Retrofit LED T8 Lamp Kit (Convert Existing Fluorescent Fixtures To LED)



ITEM NO.	DESCRIPTION
RLK-1LEDWR	Prewired Unshunted Sockets For 1 LED T8 Lamp Includes Companion Sockets
RLK-2LEDWR	Prewired Unshunted Sockets For 2 LED T8 Lamp Includes Companion Sockets
RLK-3LEDWR	Prewired Unshunted Sockets For 3 LED T8 Lamp Includes Companion Sockets
RLK-4LEDWR	Prewired Unshunted Sockets For 4 LED T8 Lamp Includes Companion Sockets
RLK-148LEDWRL15W840	Prewired Unshunted Sockets For 1 LED T8 Lamp Includes Companion Sockets
RLK-248LEDWRL15W840	Prewired Unshunted Sockets And Companion Sockets / Two 15W 1,740L LED T8 Lamps / 4000K
RLK-348LEDWRL15W840	Prewired Unshunted Sockets And Companion Sockets / Three 15W 1,740L LED T8 Lamps / 4000K
RLK-448LEDWRL15W840	Prewired Unshunted Sockets And Companion Sockets / Four 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## Retrofit Reflector Kit For Parabolics/Troffers




ITEM NO.	DESCRIPTION
RKT-22217LEDWRML9W840	2x2 / 20.75"L x 20.7"W x 2.38"H / Two 9W 1,050L LED T8 Lamps / Mirror Reflector / Unshunted Sockets / 4000K
RKT-22217LEDWRWL9W840	2x2 / 20.75"L x 20.7"W x 2.38"H / Two 9W 1,050L LED T8 Lamps / White Reflector / Unshunted Sockets / 4000K
RKT-22317LEDWRML9W840	2x2 / 20.75"L x 20.7"W x 2.38"H / Three 9W 1,050L LED T8 Lamps / Mirror Reflector / Unshunted Sockets / 4000K
RKT-22317LEDWRWL9W840	2x2 / 20.75"L x 20.7"W x 2.38"H / Three 9W 1,050L LED T8 Lamps / White Reflector / Unshunted Sockets / 4000K
RKT-24232LEDWRML15W840	2x4 / 44.75"L x 20.75"W x 2.38"H / Two 15W 1,740L LED T8 Lamps / Mirror Reflector / Unshunted Sockets / 4000K
RKT-24232LEDWRWL15W840	2x4 / 44.75"L x 20.75"W x 2.38"H / Two 15W 1,740L LED T8 Lamps / White Reflector / Unshunted Sockets / 4000K
RKT-24332LEDWRML15W840	2x4 / 44.75"L x 20.75"W x 2.38"H / Three 15W 1,740L LED T8 Lamps / Mirror Reflector / Unshunted Sockets / 4000K
RKT-24332LEDWRWL15W840	2x4 / 44.75"L x 20.75"W x 2.38"H / Three 15W 1,740L LED T8 Lamps / White Reflector / Unshunted Sockets / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.



**Choice of reflector or ballast cover**  
(For ballast cover choose strip width 4.25" or 5")



## Universal Strip Ballast Cover Kit

ITEM NO.	DESCRIPTION
RKSC-132LEDWRBL15W840	48.0"L x 4.25"W x 1.18"H / One 15W 1,740L LED T8 Lamp / Unshunted Sockets / 4000K
RKSC-232LEDWRBL15W840	48.0"L x 4.25"W x 1.18"H / Two 15W 1,740L LED T8 Lamps / Unshunted Sockets / 4000K
RKSC-132TANLEDWRBL15W840	96.0"L x 4.25"W x 1.18"H / Two 15W 1,740L LED T8 Lamps / Unshunted Sockets / 4000K
RKSC-232TANLEDWRBL15W840	96.0"L x 4.25"W x 1.18"H / Four 15W 1,740L LED T8 Lamps / Unshunted Sockets / 4000K
RKSC-132LEDWRB5L15W840	48.0"L x 5.2"W x 1.18"H / One 15W 1,740L LED T8 Lamp / Unshunted Sockets / 4000K
RKSC-232LEDWRB5L15W840	48.0"L x 5.2"W x 1.18"H / Two 15W 1,740L LED T8 Lamps / Unshunted Sockets / 4000K
RKSC-132TANLEDWRB5L15W840	96.0"L x 5.2"W x 1.18"H / Two 15W 1,740L LED T8 Lamps / Unshunted Sockets / 4000K
RKSC-232TANLEDWRB5L15W840	96.0"L x 5.2"W x 1.18"H / Four 15W 1,740L LED T8 Lamps / Unshunted Sockets / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## Universal Strip Retrofit Kit With Reflector




ITEM NO.	DESCRIPTION
RKSR-132LEDWRWL15W840	48.0"L x 9.25"W / One 15W 1,740L LED T8 Lamp / White Reflector / Unshunted Sockets / 4000K
RKSR-232LEDWRWL15W840	48.0"L x 9.25"W / Two 15W 1,740L LED T8 Lamps / White Reflector / Unshunted Sockets / 4000K
RKSR-132TANWRWL15W840	96.0"L x 9.25"W / Two 15W 1,740L LED T8 Lamps / White Reflector / Unshunted Sockets / 4000K
RKSR-232TANLEDWRWL15W840	96.0"L x 9.25"W / Four 15W 1,740L LED T8 Lamps / White Reflector / Unshunted Sockets / 4000K
RKSR-132LEDWRML15W840	48.0"L x 9.25"W / One 15W 1,740L LED T8 Lamp / Mirror Reflector / Unshunted Sockets / 4000K
RKSR-232LEDWRML15W840	48.0"L x 9.25"W / Two 15W 1,740L LED T8 Lamps / Mirror Reflector / Unshunted Sockets / 4000K
RKSR-132TANLEDWRML15W840	96.0"L x 9.25"W / Two 15W 1,740L LED T8 Lamps / Mirror Reflector / Unshunted Sockets / 4000K
RKSR-232TANLEDWRML15W840	96.0"L x 9.25"W / Four 15W 1,740L LED T8 Lamps / Mirror Reflector / Unshunted Sockets / 4000K

For enhanced light output add a mirrored specular reflector (M) or white reflector (W).

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

ITEM NO.	DESCRIPTION
<b>Universal Strip Kit Accessory</b>	
M-SKRUSB	RKSC/RKSR Series Socket Plate



Universal socket bar M-SKRUSB is ideal to retrofit 4.25" or 5" strips with either reflector or ballast cover

## UL Listed With All Options & Accessories!

### Optional Dimming:

The 4ft. lamps are available with a dimming option. Specially designed dimming lamps require an external driver that runs up to 4 lamps. Dimming driver is installed in the fixture with dimming lamps to dim with 0-10V to 10%.

# EZLED

## 4ft. Wall Fixture

### ITEM NO.

### DESCRIPTION

155-232LEDL15W840

48.0"L x 4.4"W x 4.5"H / Two 15W 1,740L LED T8 Lamps / White Finish Standard / 4000K

Add "INV5" for integrated inverter. Add "OA" for opal acrylic lens. Consult for other lamping options. Also available in 30K, 35K & 50K.

## 4ft. Stairwell With Ultrasonic Sensor

### ITEM NO.

### DESCRIPTION

155SW-232LEDL15W840

48.0"L x 4.4"W x 4.5"H / Two 15W 1,740L LED T8 Lamps / White Finish Standard / 4000K

Add "INV5" for integrated inverter. Add "OA" for opal acrylic lens. Also available in 30K, 35K & 50K.

## 4"x 4" Linear Wall

### ITEM NO.

### DESCRIPTION

L44-W117LEDWHSFL9W840

24"L x 4"W x 4"H / One 9W 1,050L LED T8 Lamp / White Finish / Frosted Lens / 4000K

L44-W217LEDWHSFL9W840

24"L x 4"W x 4"H / Two 9W 1,050L LED T8 Lamps / White Finish / Frosted Lens / 4000K

L44-W132LEDWHSFL15W840

48"L x 4"W x 4"H / One 15W 1,740L LED T8 Lamp / White Finish / Frosted Lens / 4000K

L44-W232LEDWHSFL15W840

48"L x 4"W x 4"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

L44-W132TANLEDWHSFL15W840

96"T x 4"W x 4"H / Two 15W 1,740 LED T8 Lamps / White Finish / Frosted Lens / 4000K

L44-W232TANLEDWHSFL15W840

96"T x 4"W x 4"H / Four 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

Change "SF" to "MW" (matte white), "S5" (specular parabolic), "LV" (baffled louver), or "A" (prismatic acrylic) for lens options. Consult for other finish options. Add "INV5" for integrated inverter. Consult for upright options. Also available in 30K, 35K & 50K.

## 6"x 6" Linear Wall

### ITEM NO.

### DESCRIPTION

L66-W117LEDWHSFL9W840

23.94"L x 5.75"W x 6.0"H / One 9W 1,050L LED T8 Lamp / White Finish / Frosted Lens / 4000K

L66-W217LEDWHSFL9W840

23.94"L x 5.75"W x 6.0"H / Two 9W 1,050L LED T8 Lamps / White Finish / Frosted Lens / 4000K

L66-W132LEDWHSFL15W840

47.94"L x 5.75"W x 6.0"H / One 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

L66-W232LEDWHSFL15W840

47.94"L x 5.75"W x 6.0"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

L66-W132TANLEDWHSFL15W840

95.94"L x 5.75"W x 6.0"H / Two 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

L66-W232TANLEDWHSFL15W840

95.94"L x 5.75"W x 6.0"H / Four 15W 1,740L LED T8 Lamps / White Finish / Frosted Lens / 4000K

Change "SF" to "MW" (matte white), "S5" (specular parabolic), "LV" (baffled louver), or "A" (prismatic acrylic) for lens options. Consult for other finish options. Add "INV5" for integrated inverter. Consult for upright options. Also available in 30K, 35K & 50K.

## Bed Light



ITEM NO.	DESCRIPTION
158-1U1D17LEDBAFL9W840	24.2"L x 5.4"W x 4.4"H / Two 9W 1,050L LED T8 Lamps / 1 Lamp Up 1 Lamp Down / Front Baffle / 4000K
158-1U1D32LEDBAFL15W840	48.0"L x 5.4"W x 4.4"H / Two 15W 1,740L LED T8 Lamps / 1 Lamp Up 1 Lamp Down / Front Baffle / 4000K
158-1U2D17LEDBAFL9W840	24.2"L x 5.4"W x 4.4"H / Three 9W 1,050L Led T8 Lamps / 1 Lamp Up 2 Lamps Down / Front Baffle / 4000K
158-1U2D32LEDBAFL15W840	48.0"L x 5.4"W x 4.4"H / Three 15W 1,740L LED T8 Lamps / 1 Lamp Up 2 Lamps Down / Front Baffle / 4000K
158-2U1D17LEDBAFL9W840	24.2"L x 5.4"W x 4.4"H / Three 9W 1,050L Led T8 Lamps / 2 Lamps Up 1 Lamp Down / Front Baffle / 4000K
158-2U1D32LEDBAFL15W840	48.0"L x 5.4"W x 4.4"H / Three 15W 1,740L LED T8 Lamps / 2 Lamps Up 1 Lamp Down / Front Baffle / 4000K
158-2U2D17LEDBAFL9W840	24.2"L x 5.4"W x 4.4"H / Four 9W 1,050L LED T8 Lamps / 2 Lamps Up 2 Lamps Down / Front Baffle / 4000K
158-2U2D32LEDBAFL15W840	48.0"L x 5.4"W x 4.4"H / Four 15W 1,740L LED T8 Lamps / 2 Lamps Up 2 Lamps Down / Front Baffle / 4000K

Add "INV5" for integrated inverter. Add "GCO" for grounded convenience outlet (North American 3 prong). Add "PS" for 2 way switching pull chain, or "3PS" for 4 position pull chain (up/down). Also available in 30K, 35K & 50K.

## Wide Body Garage Light



ITEM NO.	DESCRIPTION
VWCL-332LEDL15W840	48.0"L x 7.3"W x 4.12"H / Three 15W 1,740L LED T8 Lamps / 4000K
VWCL-332LEDL15W840OS(21)	48.0"L x 7.3"W x 4.12"H / Three 15W 1,740L LED T8 Lamps / 4000K / Occupancy Sensor

Add "INV5" for integrated inverter. Surface mounting brackets included. "OS" is a standard occupancy sensor. For wet location, change to "OSW", and for cold weather sensor change to "OSC". Consult for different lens and mounting options. Also available in 30K, 35K & 50K.

## Spill Ring Bath



ITEM NO.	DESCRIPTION
MFL-217LEDSL15W840	24.75"L x 6.0"W x 4.25"H / Two 9W 1,050L LED T8 Lamps / Satin Nickel Finish / 4000K
MFL-232LEDSL15W840	48.60"L x 6.0"W x 4.25"H / Two 15W 1,740L LED T8 Lamps / Satin Nickel Finish / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.

## End Cap Bath



ITEM NO.	DESCRIPTION
VB-217LEDIVL15W840	25.5"L x 4.75"W x 4.0"H / Two 9W 1,050L LED T8 Lamps / Ivory End Cap / White Smooth Lens Standard
VB-232LEDIVL15W840	49.5"L x 4.75"W x 4.0"H / Two 15W 1,740L LED T8 Lamps / Ivory End Cap / White Smooth Lens Standard

Add "INV5" for integrated inverter. For other end cap options, see page 45. Also available in 30K, 35K & 50K.

## Wall Puff



ITEM NO.	DESCRIPTION
WP-217LEDL15W840	27.0"L x 6.0"W x 2.75"H / Two 9W 1,050L LED T8 Lamps / 4000K
WP-232LEDL15W840	51.0"L x 6.0"W x 2.75"H / Two 15W 1,740L LED T8 Lamps / 4000K

Add "INV5" for integrated inverter. Also available in 30K, 35K & 50K.



## Popular Bypass Single Ended

ITEM NO.	DESCRIPTION
LT8BG48L15W1740L40K	48"L / Single Ended Bypass T8 Lamp / Frosted Glass / 15W 1,740L / 4000K



## Standard Bypass Single Ended

ITEM NO.	DESCRIPTION
LT8BGC24L9W1050L40K	24"L / Single Ended Bypass T8 Lamp / Plastic Coated Glass / 9W 1,050L / 4000K
LT8BGC36L12W1200L40K	36"L / Single Ended Bypass T8 Lamp / Plastic Coated Glass / 12W 1,200L / 4000K
LT8BGC48L15W1740L40K	48"L / Single Ended Bypass T8 Lamp / Plastic Coated Glass / 15W 1,740L / 4000K



## Premium Bypass Single Ended

ITEM NO.	DESCRIPTION
L10T8BGC48L12W1750L40K	48"L / Premium Single Ended Bypass T8 Lamp / Plastic Coated Glass / 12W 1,750L / 4000K / 10 Year Warranty
L10T8BGC48L15W2000L40K	48"L / Premium Single Ended Bypass T8 Lamp / Plastic Coated Glass / 15W 2,000L / 4000K / 10 Year Warranty
L10T8BGC48L18W2500L40K	48"L / Premium Single Ended Bypass T8 Lamp / Plastic Coated Glass / 18W 2,500L / 4000K / 10 Year Warranty



## High Output Bypass Single Ended

ITEM NO.	DESCRIPTION
LT8BGC48L26W3500L40K	48"L / High Output Single Ended Bypass T8 Lamp / Plastic Coated Glass / 26W 3,500L / 4000K



## Bypass Double Ended Or Single Ended

ITEM NO.	DESCRIPTION
LT8BDGC48L18W2100L40K	48"L / Double & Single Ended Bypass T8 Lamp / Plastic Coated Glass / 18W 2,100L / 4000K
L10T8BDGC48L12W1750L40K	48"L / Double & Single Ended Bypass T8 Lamp / Plastic Coated Glass / 12W 1,750L / 4000K / 10 Year Warranty
L10T8BDGC48L18W2500L40K	48"L / Double & Single Ended Bypass T8 Lamp / Plastic Coated Glass / 18W 2,500L / 4000K / 10 Year Warranty



## Dual Type A & Type B (Magic Tube)

### ITEM NO.

### DESCRIPTION

LT8ABP48L18W2250L40K	48"L / Single Ended T8 Lamp Type A & B / Plastic / 18W 2,250L / 4000K
LT8ABP48L15W1875L40K	48"L / Single Ended T8 Lamp Type A & B / Plastic / 15W 1,875L / 4000K
LT8ABP24L15W1875L40K	24"L / Single Ended T8 Lamp Type A & B / Plastic / 15W 1,875L / 4000K

## Dimming Bypass Single Ended

### ITEM NO.

### DESCRIPTION

LD2T8BGC48L18W2200L40K	48"L / 2 Wire Dimming Single Ended Bypass T8 Lamp / 18W 2,200L / 4000K
------------------------	--

## Dimming Type C (Driver & Tubes)

### ITEM NO.

### DESCRIPTION

JIGZYDRWG192	3 Light 60W 0-10V Dimmable Driver
JIGZDRWG211	2 Light 40W 0-10V Dimmable Driver
JIGZYT810W600BOT40K	24"L / LED T8 DIM / 10W 1,200L / 4000K
JIGZYT8181200BONT40KFUS	48"L / LED T8 DIM / 18W 2,100 Lumens / 4000K

## T5HO Bypass Single Ended

### ITEM NO.

### DESCRIPTION


LT5BG46L25W3300L40K	46"L / T5HO Single Ended Bypass T5 Lamp / Frosted Glass / 25W 3,300L / 4000K
---------------------	--

## Type A Ballast Compatible

### ITEM NO.

### DESCRIPTION



LT8AG48L13W1900L40K	48"L / T8 Ballast Compatible / Glass / 13W 1,900L / 4000K
---------------------	---



*Coming Soon!*



**Full LED  
Color Tuning**



2700K

3500K

4000K


5000K

**White Color Tuning**  
Switch seamlessly from  
2700K to 5000K and  
anything inbetween!





***RGBW Single Ended  
LED Lamps That Work  
With DMX Control!***





# INDEX

Part Number	Page #	Part Number	Page #	Part Number	Page #	Part Number	Page #
1	16, 100	AIOCBF	28	ELXTEU	83	L23R	47
15	37, 99	AIOCLF	49	ERB	68	L44	25
41	19	AIOCSA	27,28	ESB	68	L44IRR	23
42	19,38, 100	AIOCSB	27,28	EZRXTEU	83	L44IRR	48
44	18, 19, 99	AIOCSR	29	EZXTEU	83	L44P	22,25, 95
68	62	AIOCSW	29	FHBC	12, 101	L44R	47
69	62	AOD	66	FHBF	101	L44R	48, 94
74	42	ATP	23	FHBFN	102	L44S	35
79	42	BOLMA6	81	FHBI	101	L44W	41, 106
155	43, 106	C	40, 98	FHBR	13, 102	L45	42,23
158	43, 107	CEU	85	FHBX	13		24, 95,47, 48, 94, 36, 42, 106
741	42	CIR	34	FLEDR2	87	L66	
769	36, 98	CL45	43	FLM	80	LCTXTEU	86
770	37, 99	CLP	39	FLMM	80	LD23	15,22, 96
771	36	CLPU	85	GLO	68	LD23R	47
772	37, 99	CPYRA	67	GRPL	81	LD23RF	95
791	42	CPYSA	67	HBIA	10	LD2T8	109
10M	38	CRCS	38	HBPA	10	LDA	15,21
10T5	18	CTC	62	HBRMSR	13	LED-2350048	80
10T5S	18	CTCE	63	HLCWLEZU	86	LED-2375069	80
10T5SW	15,18	CTCM	64	HLEMR16	88	LED-98000	82
10T5W	18	CWN	40, 98	HLRHLED16	89	LEDCXTEU	85
155SW	44, 106	CXTEU	85	HLWLEZU	84	LEDR1	87
155SWR	44	D2D	78	ILS	34	LEDR2	87
155SWS	44	DBELACEM	88	INDCWLEZU	84, 86	LEDR5	87
1FSF	17	DCSHM	78	INDEM16	88	LEDT	58, 88
42E	17	DECCD	62	INDRHLED	89	LEDTFX2	88
42SC	100	DECCE	62	INDWLEZU	84	LHBIP	11
42T	19	DECWD	64	JIGZ	109	LIS	33
44FSF	15,17,45	DECWF	64	KZXTEU	83	LIWMS	43
44RSF	17	DECWV	64	L10T8	109	LLCFR	50
44RSR	17	DIS	34	L10T8BD	108	LLCRA	30
772N	37, 99	DLV6	34, 96	L10T8BGC	108	LLCRB	30
ABL3	6	DXR	87	L23	20,35,41		



# INDEX

Part Number	Page #	Part Number	Page #	Part Number	Page #	Part Number	Page #
LLCSA	31	MGC	77	PLELRXTEU	83	SKB	52
LLCSB	31	MGO	72	PRF1	66	SKY	55
LLCSC	31	MGP	72	PWL	44	SLT	66
LLCSH	30	MHI	73	RAV	56	SMKT-MFPEL	53
LLCSR	50	MHO	76	RCS	100	SPR	97
LLP	32	MHT	76	RDICB	94	SPS	90
LLW	42	MHUT	73	RDIS	53, 54, 93	SQ44	25
LPLI	95	MHZ	73	RDISA	53, 54	SRDIS	97
LPLIA	32	MILGCOWPKSR	78	RDISD	55,93	SRDISD	98
LPS	91	MILGWPKPKSR	78	RDISE	54	SRG	36, 97
LSBR	19	MIMDCOWPKSR	78	RELZXTE	84	STWR	44
LT5BG	109	MIMDWPKPKSR	78	RG	56, 57, 92	SVP	66, 70
LT8AB	109	MIPK	82	RGAIR	56	TVP	38
LT8AG	109	MISMRWPK	78	RGCRV	55	VB	45, 107
LT8BDG	108	MKR	76	RH	9	VW	65, 102
LT8BG	108	MLEDDUCL	58	RKBC	61, 103	VWCL	107
LT8BGC	108	MLUC	58	RKBCF	60	VWFHB	14, 102
LTP	96	MLUCR	58	RKBCR	60	VWHBS	14
MAO	75	MNG	72	RKDIS	59	VWN	66
MAPW	75	MNO	72	RKDISE	59	WLEZXTEU	84
MBBP	70	MOCL	69	RKFSE	61	WLPC	70
MBR	74	MPR	74	RKPWL	61	WMPC	70
MCBP	70	MPS	90	RKSC	105	WP	45, 107
MCE	39	MRRS	16	RKSEOS	61	WRC	69
MCEO	71	MSCW	75	RKSR	105	WSC	69
MCER	71	MSN	70	RKT	60,104	WSPC	70
MCH	39, 98	MTDLOS	63	RLK	104	X44	26
MCO	74	MTO	77	RMR16	87	ZMS	100
MDC	40	MVP	69	RMR16WP	88		
MDH5	75	MW4A	38	ROL	48		
MFL	107	MWCD	68	RP	55, 93		
MFLBD	45	MWCTRD	69	RWW	55		
MFN	77	MWCTRS	69	SAL	79		
MFPEL	53	PER	51	SALSR	79		

# Manufacturer's Limited Warranty

**A.** Mobern Lighting warrants that all of its "legacy" Fluorescent or HID Product(s), other than ballasts, emergency battery packs, lamps and poles supplied in connection therewith, will be free from defects in workmanship and materials for a period of three (3) years from date of shipment (the "Warranty"). **SUCH WARRANTY IS IN LIEU OF ANY OTHER WARRANTIES INCLUDING WITHOUT LIMITATION, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** Mobern Lighting, at its option, will repair or replace, F.O.B. our factory, freight prepaid, any Mobern Lighting Product(s), other than ballasts, emergency battery packs, lamps and poles supplied in connection therewith, which are deemed, in its sole and absolute discretion, defective in workmanship or materials. Such repair or replacement is the sole and exclusive remedy available to any customer to rectify defects in Mobern Lighting Product(s), other than defects in ballasts, emergency battery packs, lamps and poles sold in connection therewith. Ballasts, lamps and poles are covered by separate manufacturer or factory warranties, if applicable at the time of defect. Therefore, each Mobern Lighting customer or end-user must timely notify Mobern Lighting or the manufacturer directly (if directed to do so by Mobern Lighting) in order to preserve the applicable manufacturer's warranty available under this provision. **CUSTOMER OR END-USER FAILURE TO TIMELY COMPLY WITH THIS NOTICE PROVISION MAY VOID THE MANUFACTURER WARRANTY.**

**B.** Mobern Lighting warrants that all of its indoor and outdoor light emitting diode (LED) fixtures, including the LED array, LED drivers and integral control devices, are free of defects in workmanship and materials for a period of five (5) years from the date of shipment. Unless otherwise expressly stated in writing, the LED array will be considered defective if a total of 15% or more of the individual light emitting diodes fail to illuminate. Mobern Lighting reserves the right to determine, in its sole and absolute discretion, whether to repair or replace defective LED fixtures or components. No charge-back, or reimbursement for in-the-field labor or material, or delay in installation, that results from defective products, will be honored, accepted or paid for by Mobern Lighting, unless expressly authorized in writing by Mobern Lighting. In no event shall any inside salesperson or outside sales agent of Mobern Lighting have the authority to bind Mobern Lighting to any such charge under this Warranty. LED boards, drivers and other components are covered by separate manufacturer or factory warranties, if applicable at the time of defect. Therefore, each Mobern Lighting customer or end-user must timely notify Mobern Lighting or the manufacturer directly (if directed to do so by Mobern Lighting) in order to preserve the applicable manufacturer's warranty available under this provision. **CUSTOMER OR END-USER FAILURE TO TIMELY COMPLY WITH THIS NOTICE PROVISION MAY VOID THE MANUFACTURER WARRANTY.**

**C.** This Statement of Limited Warranty applies only when Mobern's product(s) are installed in applications in which ambient temperatures are within the range of specified operating temperatures and are operated within the electrical values shown on the ballast or LED driver label. Mobern Lighting will not be responsible for any failure of any Mobern product(s) that results from external causes such as: acts of nature; physical damage; exposure to adverse or hazardous chemical or other substances; use of reactive cleaning agents and/or harsh chemicals to clean Mobern's product(s); environmental conditions; vandalism; fire; power failure, improper power supply, power surges or dips, and/or excessive switching; induced vibration; animal or insect activity; fault or negligence of purchaser, any end user of Mobern product(s) and/or any third party not engaged by Mobern Lighting; improper or unauthorized use, installation, handling, storage, alteration, maintenance or service, including failure to abide by any product classifications or certifications, or failure to comply with any applicable standards, codes, recommendations, product specification sheets, or instructions of Mobern Lighting; use of Mobern's product(s) with products, processes or materials supplied by any end user or third party; or, any other occurrences beyond Mobern Lighting's reasonable control. Also, Mobern Lighting will not be responsible for any substantial deterioration in fixture paint finish that is caused by failure to clean, inspect, handle or maintain.

**D.** Sensors, controls, emergency battery packs, lamps and poles are covered by separate manufacturer's warranties. Therefore, each Mobern Lighting customer or end-user must timely notify Mobern Lighting or the manufacturer directly (if directed to do so by Mobern Lighting) in order to preserve the applicable manufacturer's warranty available under this provision. **CUSTOMER OR END-USER FAILURE TO TIMELY COMPLY WITH THIS NOTICE PROVISION MAY VOID THE MANUFACTURER WARRANTY.**

**E. IN NO EVENT SHALL MOBERN LIGHTING BE RESPONSIBLE TO REPAIR OR REPLACE ANY PRODUCT THAT WAS NOT USED FOR ITS INTENDED PURPOSE OR THAT WAS INSTALLED OR MODIFIED IN ANYWAY NOT IN ACCORDANCE WITH MOBERN LIGHTING'S EXPRESS WRITTEN INSTRUCTION.**

**F.** No agent, employee or representative of Mobern Lighting has any authority to bind Mobern Lighting to any affirmation, representation or warranty concerning Products sold by Mobern Lighting unless authorized to do so in writing.





**MOBERN**  
LIGHTING

***Fair, Friendly, & Flexible - Everytime!***

  
e-mail us:  
[sales@mobern.com](mailto:sales@mobern.com)