



# Color Your Way to an Improved Workplace.

**BBP<sup>®</sup>37 COLOR AND CUT  
SIGN & LABEL PRINTER**

**BBP<sup>®</sup>35 MULTICOLOR  
SIGN & LABEL PRINTER**

# Color Your Way to an Improved Workplace



## Setting the New Standard in Safety & Facility Identification

Because safety and productivity mean the world to you, it's time to step up to the new standard by creating signs and labels that demand attention. After all, effective workplace visuals make all the difference in taking your facility to the next level by giving employees the information they need right at a glance.

**And now there's a tool to do it all!**

Brady's BBP®35 and BBP®37 sign and label printers give you the power to make signs and labels in the colors and shapes you need to make an impact – right at your own facility and right when you need them. With remarkable multi-color printing, versatile shape-cutting capabilities and impressively fast print speeds, you'll never know how you lived without one of these printers.

### Facility & Safety ID

Pre-Printed GHS/CLP Chemical Labels.....	5
Indoor/Outdoor Vinyl .....	6
Low-Halide Polyester .....	7
Pre-Printed Pre-Cut Blank Sign Headers.....	8
Non-Adhesive Tags .....	8
ToughWash® Washdown Resistant Labels.....	9
Printable Magnetic Supply.....	9
ToughStripe® Printable Floor Tape .....	10
Repositionable Vinyl.....	10
Retro Reflective Labels .....	11
BradyGlo Photoluminescent Tape .....	11
Cold Temperature Material .....	11
Circle Gauge Labels.....	12
Gradient "Ruler" Labels.....	12
Arc Flash Labels.....	13
Make Your Own Rigid Valve Tags .....	13
Blank Rigid Panels .....	14
Product ID Materials.....	15
Tamper-Evident Asset ID Labels .....	15
Raised Profile Labels (Rectangular).....	16
Raised Profile Labels (Push Button) .....	17
<b>Starter Kits .....</b>	<b>18-19</b>
<b>Print Ribbons.....</b>	<b>20-21</b>
<b>Software .....</b>	<b>22</b>
<b>Printers &amp; Accessories.....</b>	<b>23</b>

**BBP<sup>®</sup>37**  
COLOR & CUT  
SIGN & LABEL PRINTER

**BBP<sup>®</sup>35**  
MULTICOLOR SIGN & LABEL PRINTER

**Faster.  
Easier.  
More  
Versatile.  
Expect  
Nothing  
Less!**



### Multiple Print Colors

- Print signs and labels that are more noticeable, more memorable and effective
- Color is the differentiator when you need to effectively improve workplace safety and productivity



### Shape Cutting

- Revolutionary built-in XY plotter-cutter system in the BBP37 printer
- Cut out shapes and text, or cut around your message to create labels that look and fit just how you want them to



### Label Making Made Easy

- Incredibly easy and intuitive
- Ideal for multiple users, centralized locations and lean 5S events
- Compatible with powerful Brady Workstation Label Apps for added versatility



### Automatic Label Setup

- Printers read critical information from the supply cartridge and then automatically set up the label attributes so you can start printing immediately
- No more calibration or wasted labels, no print speed/burn temperature trial labels, no scrolling through screens to select a label and no wasted time setting up label dimensions or text size

### 20-second Material Changeovers

- “Drop in” ribbons and labels mean no complicated threading, assembling spindles, sensor adjustment or calibration steps
- You can get on with the job faster, giving you more time for other tasks

### 5 Inches per Second Print Speed

- Fast processing time and print speed mean you don't have to wait around for your labels





## Legendary Material Performance

- Brady labels are reliable and durable because we design labels in our own facilities and put them through rigorous R&D tests and trials before they're ready for use
- Nothing leaves our doors without meeting our standards
- Some last up to 10 years outdoors. Stick to rough surfaces or smooth; dirty surfaces or clean; in harsh conditions or normal conditions. With that kind of reliability, you'll only need to make these labels once

## Options. Lots of Options

- Print pipe labels, GHS chemical labels, labels that glow in the dark and labels that aren't even labels at all (they're tags!)
- With over 300 parts in all, you can label it all!
- Any "B30" label or ribbon supply is compatible for use in BBP35 and 37 sign and label printers, if it was manufactured after September 1, 2015



This icon indicates that a particular part can be XY-Plotter cuttable in the BBP37 printer model. Shapes and 0.75" or taller text can be cut from these materials.





## Pre-Printed GHS / CLP Chemical Labels (B-7569)

- Blank labels with pre-printed red diamonds allow the printer to produce 2-color GHS / CLP labels in one print pass
- 3 sizes of labels, each with 6 diamond layouts that match templates in the Brady Workstation GHS App
- Indoor/outdoor vinyl material and durable inks withstand exposure to moisture, chemicals and handling
- You can also make GHS labels with white tape and black/red ribbon to reduce your supply inventory

Service Temp: -4°F to 180°F Application Temp: 50°F to 180°F  
Average Outdoor Durability: 3-5 years



Fits Printer Model(s)	Catalog #	B#	Material	Legend	Label Height Inch (mm)	Label Width Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon	
BBP37,35, 31, 33	B30-260-7569-CLP1	B-7569	Vinyl		L1 Diamond + Text	2.170 (55.0)	3.350 (85.0)	1	340	B30-R10000
BBP37,35, 31, 33	B30-261-7569-CLP1	B-7569	Vinyl		L1 Diamond + Text	2.950 (75.0)	4.330 (110.0)	1	270	B30-R10000
BBP37,35, 31, 33	B30-262-7569-CLP1	B-7569	Vinyl		L1 Diamond + Text	4.130 (105.0)	6.100 (155.0)	1	200	B30-R10000
BBP37,35, 31, 33	B30-260-7569-CLP2	B-7569	Vinyl		L2 Diamond + Text	2.170 (55.0)	3.350 (85.0)	1	340	B30-R10000
BBP37,35, 31, 33	B30-261-7569-CLP2	B-7569	Vinyl		L2 Diamond + Text	2.950 (75.0)	4.330 (110.0)	1	270	B30-R10000
BBP37,35, 31, 33	B30-262-7569-CLP2	B-7569	Vinyl		L2 Diamond + Text	4.130 (105.0)	6.100 (155.0)	1	200	B30-R10000
BBP37,35, 31, 33	B30-260-7569-CLP3A	B-7569	Vinyl		L3A Diamond + Text	2.170 (55.0)	3.350 (85.0)	1	340	B30-R10000
BBP37,35, 31, 33	B30-261-7569-CLP3A	B-7569	Vinyl		L3A Diamond + Text	2.950 (75.0)	4.330 (110.0)	1	270	B30-R10000
BBP37,35, 31, 33	B30-262-7569-CLP3A	B-7569	Vinyl		L3A Diamond + Text	4.130 (105.0)	6.100 (155.0)	1	200	B30-R10000
BBP37,35, 31, 33	B30-260-7569-CLP3B	B-7569	Vinyl		L3B Diamond + Text	2.170 (55.0)	3.350 (85.0)	1	340	B30-R10000
BBP37,35, 31, 33	B30-261-7569-CLP3B	B-7569	Vinyl		L3B Diamond + Text	2.950 (75.0)	4.330 (110.0)	1	270	B30-R10000
BBP37,35, 31, 33	B30-262-7569-CLP3B	B-7569	Vinyl		L3B Diamond + Text	4.130 (105.0)	6.100 (155.0)	1	200	B30-R10000
BBP37,35, 31, 33	B30-260-7569-CLP4A	B-7569	Vinyl		L4A Diamond + Text	2.170 (55.0)	3.350 (85.0)	1	340	B30-R10000
BBP37,35, 31, 33	B30-261-7569-CLP4A	B-7569	Vinyl		L4A Diamond + Text	2.950 (75.0)	4.330 (110.0)	1	270	B30-R10000
BBP37,35, 31, 33	B30-262-7569-CLP4A	B-7569	Vinyl		L4A Diamond + Text	4.130 (105.0)	6.100 (155.0)	1	200	B30-R10000
BBP37,35, 31, 33	B30-260-7569-CLP4B	B-7569	Vinyl		L4B Diamond + Text	2.170 (55.0)	3.350 (85.0)	1	340	B30-R10000
BBP37,35, 31, 33	B30-261-7569-CLP4B	B-7569	Vinyl		L4B Diamond + Text	2.950 (75.0)	4.330 (110.0)	1	270	B30-R10000
BBP37,35, 31, 33	B30-262-7569-CLP4B	B-7569	Vinyl		L4B Diamond + Text	4.130 (105.0)	6.100 (155.0)	1	200	B30-R10000



### Brady WorkStation has a GHS Label App!

- Built-in pre-formatted label layouts and approved GHS symbols
- Pre-worded hazard statements and GHS symbols that just click and drag into the layout (no need to type everything in)
- Once you create a label, the data is there and you can print any size with only a single click
- Automatic "block-out" of unused diamonds on pre-printed supplies so you can inventory fewer label rolls
- No driver needed when connected to a Brady BBP®35, 37, 31, 33 or 85 printer





## Indoor/Outdoor Vinyl (B-595)

- For general facility and safety identification: Our best industrial vinyl yet
- Durable, low-shrink vinyl with our most aggressive adhesive
- Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper-jacketed pipes, powder-coated surfaces)
- Adheres to “difficult” low-surface energy items (PVC piping, blow-molded equipment cases, ABS plastics, recycled plastics)

Service Temp: -40°F to 180°F Application Temp: 0°F to 180°F  
 Average Outdoor Durability: 8-10 year outdoor vinyl label durability.  
 Agency approvals: RoHS




Figure 33

### Facility and Safety Applications:

- 5S Labels
- Pipe Markers
- Safety & Warning Labels
- Equipment & Panel Labels
- Arc Flash & Chemical Labels
- And More!

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP37,35,31,33	Fig. 33	B30C-500-595-WT	B-595	White	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-1125-595-WT	B-595	White	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-2250-595-WT	B-595	White	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-3000-595-WT	B-595	White	3.000 (76.2)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-4000-595-WT	B-595	White	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-YL	B-595	Yellow	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-1125-595-YL	B-595	Yellow	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-2250-595-YL	B-595	Yellow	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-3000-595-YL	B-595	Yellow	3.000 (76.2)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-4000-595-YL	B-595	Yellow	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-RD	B-595	Red	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-1125-595-RD	B-595	Red	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-2250-595-RD	B-595	Red	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-4000-595-RD	B-595	Red	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-BL	B-595	Blue	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-1125-595-BL	B-595	Blue	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-2250-595-BL	B-595	Blue	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-4000-595-BL	B-595	Blue	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-GN	B-595	Green	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-1125-595-GN	B-595	Green	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-2250-595-GN	B-595	Green	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-4000-595-GN	B-595	Green	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-OR	B-595	Orange	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-1125-595-OR	B-595	Orange	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-2250-595-OR	B-595	Orange	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-4000-595-OR	B-595	Orange	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-BK	B-595	Black	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-1125-595-BK	B-595	Black	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-2250-595-BK	B-595	Black	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-4000-595-BK	B-595	Black	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-BR	B-595	Brown	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-1125-595-BR	B-595	Brown	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-2250-595-BR	B-595	Brown	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-4000-595-BR	B-595	Brown	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-GD	B-595	Gold	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-1125-595-GD	B-595	Gold	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-2250-595-GD	B-595	Gold	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-4000-595-GD	B-595	Gold	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-GY	B-595	Gray	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-1125-595-GY	B-595	Gray	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-2250-595-GY	B-595	Gray	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-4000-595-GY	B-595	Gray	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-PL	B-595	Purple	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-1125-595-PL	B-595	Purple	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-2250-595-PL	B-595	Purple	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35,31,33	Fig. 33	B30C-4000-595-PL	B-595	Purple	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ☒
BBP37,35,31,33	Fig. 33	B30C-500-595-CL	B-595	Clear	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-1125-595-CL	B-595	Clear	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-2250-595-CL	B-595	Clear	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-4000-595-CL	B-595	Clear	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ☒

U.S. Patent Nos. 5,823,689; 6,570,602. Additional Patents Pending.



## Low-Halide Polyester (B-569)

- Low-halide content for labeling stainless steel pipes and surfaces
- Applies best to very smooth surfaces and ideal for mounting to rigid panels

Service Temp: -40°F to 212°F Application Temp: 0°F to 212°F  
Average Outdoor Durability: 3-5 years




Figure 33

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP37,35, 31, 33	Fig. 33	B30C-500-569-WT	B-569	White	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-WT	B-569	White	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-WT	B-569	White	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-3000-569-WT	B-569	White	3.000 (76.2)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-WT	B-569	White	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-YL	B-569	Yellow	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-YL	B-569	Yellow	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-YL	B-569	Yellow	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-YL	B-569	Yellow	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-RD	B-569	Red	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-RD	B-569	Red	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-RD	B-569	Red	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-RD	B-569	Red	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-BL	B-569	Blue	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-BL	B-569	Blue	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-BL	B-569	Blue	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-BL	B-569	Blue	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-LB	B-569	Light Blue	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-LB	B-569	Light Blue	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-LB	B-569	Light Blue	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-LB	B-569	Light Blue	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-SB	B-569	Sky Blue	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-SB	B-569	Sky Blue	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-SB	B-569	Sky Blue	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-SB	B-569	Sky Blue	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-GN	B-569	Green	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-GN	B-569	Green	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-GN	B-569	Green	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-GN	B-569	Green	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-OR	B-569	Orange	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-OR	B-569	Orange	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-OR	B-569	Orange	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-OR	B-569	Orange	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-BK	B-569	Black	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-BK	B-569	Black	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-BK	B-569	Black	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-BK	B-569	Black	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-BR	B-569	Brown	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-BR	B-569	Brown	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-BR	B-569	Brown	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-BR	B-569	Brown	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-OC	B-569	Ochre	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-OC	B-569	Ochre	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-OC	B-569	Ochre	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-OC	B-569	Ochre	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-TN	B-569	Tan	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-TN	B-569	Tan	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-TN	B-569	Tan	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-TN	B-569	Tan	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-GY	B-569	Gray	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-GY	B-569	Gray	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-GY	B-569	Gray	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-GY	B-569	Gray	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-PL	B-569	Purple	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-PL	B-569	Purple	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-PL	B-569	Purple	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-PL	B-569	Purple	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000-WT ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-PK	B-569	Pink	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-PK	B-569	Pink	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-PK	B-569	Pink	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-PK	B-569	Pink	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-569-CL	B-569	Clear	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-569-CL	B-569	Clear	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-569-CL	B-569	Clear	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-569-CL	B-569	Clear	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂



## Pre-Printed Pre-Cut Blank Sign Headers (B-595)

- Allows printer to create multicolor signs fast - in a single print pass
- Headers meet NFPA 70E, OSHA 1910.145 and ASME/ANSI Z535 standards
- Indoor/outdoor grade material conforms to rough, highly textured and "difficult to adhere to" surfaces

Service Temp: -40°F to 180°F Application Temp: 0°F to 180°F  
 Average Outdoor Durability: 8-10 years  
 Agency Approvals: RoHS




Figure 70

Fits Printer Model(s)	Diagram	Catalog #	B#	Material	Header	Label Height A Inch (mm)	Label Width B Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP37,35,31,33	Fig. 70	B30-241-595-OSHADA	B-595	Vinyl		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-25-595-OSHADA	B-595	Vinyl		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000
BBP37,35,31,33	Fig. 70	B30-241-595-OSHACA	B-595	Vinyl		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-25-595-OSHACA	B-595	Vinyl		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000
BBP37,35,31,33	Fig. 70	B30-241-595-ANSICA	B-595	Vinyl		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-25-595-ANSICA	B-595	Vinyl		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000
BBP37,35,31,33	Fig. 70	B30-241-595-ANSIDA	B-595	Vinyl		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-25-595-ANSIDA	B-595	Vinyl		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000
BBP37,35,31,33	Fig. 70	B30-241-595-ANSIWA	B-595	Vinyl		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-25-595-ANSIWA	B-595	Vinyl		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000
BBP37,35,31,33	Fig. 70	B30-241-595-ANSINO	B-595	Vinyl		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-25-595-ANSINO	B-595	Vinyl		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000
BBP37,35,31,33	Fig. 70	B30-242-595-BLNKWT	B-595	Vinyl		1.125 (28.6) *	2.850 (72.4)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-241-595-BLNKWT	B-595	Vinyl		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-219-595-BLNKWT	B-595	Vinyl		2.250 (57.5) *	3.850 (97.8)	1	250	B30-R10000
BBP37,35,31,33	Fig. 70	B30-25-595-BLNKWT	B-595	Vinyl		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000
BBP37,35,31,33	Fig. 70	B30-241-595-BLNKYL	B-595	Vinyl		2.250 (57.5)	3.000 (76.2)	1	300	B30-R10000
BBP37,35,31,33	Fig. 70	B30-25-595-BLNKYL	B-595	Vinyl		4.000 (101.6)	6.000 (152.4)	1	175	B30-R10000

\*Label pre-sized to fit blank rigid valve tags, but can also be used on its own as general purpose label. See page 13 for details on Valve Tags.



## Non-Adhesive Tags (B-551)

- Non-adhesive semi-rigid card stock in pre-cut and continuous styles
- Tags are pre-cut with hole or easy to hole-punch, are micro-perforated between tags to separate cleanly, and some feature chamfered corners
- Snap-in plastic grommets available for extra strength around mounting hole (Catalog #20596, 100/bag)

Service Temp: -40°F to 193°F  
 Average Outdoor Durability: Up to 2 years




Figure 33 Figure 69

Fits Printer Model(s)	Diagram	Catalog #	B#	Header	Tag Width A Inch (mm)	Tag Height B Inch (mm)	Tags Per Row	Tags Per Roll	Rec. Ribbon
BBP37,35,31,33	Fig. 69	B30-255-551-ANSIDA	B-551		3.250 (82.6)	5.750 (146.1)	1	100	B30-R10000
BBP37,35,31,33	Fig. 69	B30-255-551-OSHADA	B-551		3.250 (82.6)	5.750 (146.1)	1	100	B30-R10000
BBP37,35,31,33	Fig. 69	B30-255-551-ANSICA	B-551		3.250 (82.6)	5.750 (146.1)	1	100	B30-R10000
BBP37,35,31,33	Fig. 69	B30-255-551-WHT	B-551		3.250 (82.6)	5.750 (146.1)	1	100	B30-R10000
BBP37,35,31,33	Fig. 33	B30C-2500-551-WT	B-551		2.500 (63.5)	50ft. (15.2m)	1 roll (cont.)		B30-R10000
BBP37,35,31,33	Fig. 33	B30C-3250-551-WT	B-551		3.250 (82.6)	50ft. (15.2m)	1 roll (cont.)		B30-R10000
BBP37,35,31,33	Fig. 33	B30C-4250-551-WT	B-551		4.250 (107.9)	50ft. (15.2m)	1 roll (cont.)		B30-R10000






## ToughWash® Washdown Resistant Labels (B-854, B-855)

- Withstands high pressure, heat, harsh chemicals and numerous washdown cycles
- B-854 offers metal detectable layer to detect foreign debris in food stream
- Legible and long-lasting for even the toughest washdown cycles
- Ideal for use in the food & beverage industry

Service Temp: -40°F to 230°F  
Agency approvals: **RoHS**




Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Length B Inch (mm)	Labels Per Roll	Rec. Ribbon
<b>B-854 ToughWash™ Metal Detectable Material</b>								
BBP37,35, 31, 33	Fig. 33	B30C-4000-854-WT	B-854		4.000 (101.06)	50ft. (15.2 m)	1 roll (cont.)	B30-R6000
BBP37,35, 31, 33	Fig. 33	B30C-4000-854-YL	B-854		4.000 (101.06)	50ft. (15.2 m)	1 roll (cont.)	B30-R6000
BBP37,35, 31, 33	Fig. 73	B30C-4000-854-WARN	B-854		4.000 (101.06)	6.250 (158.8)	100	B30-R6000
BBP37,35, 31, 33	Fig. 73	B30C-4000-854-DANG	B-854		4.000 (101.06)	6.250 (158.8)	100	B30-R6000
BBP37,35, 31, 33	Fig. 73	B30C-4000-854-CAUT	B-854		4.000 (101.06)	6.250 (158.8)	100	B30-R6000
<b>B-855 ToughWash™ Material</b>								
BBP37,35, 31, 33	Fig. 33	B30C-1125-855-WT	B-855		1.125 (28.6)	50ft. (15.2 m)	1 roll (cont.)	B30-R6000
BBP37,35, 31, 33	Fig. 33	B30C-2250-855-WT	B-855		2.250 (57.5)	50ft. (15.2 m)	1 roll (cont.)	B30-R6000
BBP37,35, 31, 33	Fig. 33	B30C-4000-855-WT	B-855		4.000 (101.06)	50ft. (15.2 m)	1 roll (cont.)	B30-R6000
BBP37,35, 31, 33	Fig. 33	B30C-1125-855-YL	B-855		1.125 (28.6)	50ft. (15.2 m)	1 roll (cont.)	B30-R6000
BBP37,35, 31, 33	Fig. 33	B30C-2250-855-YL	B-855		2.250 (57.5)	50ft. (15.2 m)	1 roll (cont.)	B30-R6000
BBP37,35, 31, 33	Fig. 33	B30C-4000-855-YL	B-855		4.000 (101.06)	50ft. (15.2 m)	1 roll (cont.)	B30-R6000
BBP37,35, 31, 33	Fig. 73	B30C-4000-855-WARN	B-855		4.000 (101.06)	6.250 (158.8)	100	B30-R6000
BBP37,35, 31, 33	Fig. 73	B30C-4000-855-DANG	B-855		4.000 (101.06)	6.250 (158.8)	100	B30-R6000
BBP37,35, 31, 33	Fig. 73	B30C-4000-855-CAUT	B-855		4.000 (101.06)	6.250 (158.8)	100	B30-R6000




## Printable Magnetic Supply (B-509)

- Easiest and quickest material for removing and repositioning
- Non-adhesive magnetic material that can be printed on directly
- Ideal for reusable, repositionable, and lean / 5S identification applications

Service Temp: 0°F to 158°F  
Average Outdoor Durability: 3 to 5 years



Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP37,35, 31, 33	Fig. 33	B30C-2500-509-WT	B-509	White	2.500 (63.5)	25ft (7.62m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4250-509-WT	B-509	White	4.250 (107.8)	25ft (7.62m)	1 roll (cont.)	B30-R10000 ✖
BBP37,35, 31, 33	Fig. 33	B30C-2500-509-YL	B-509	Yellow	2.500 (63.5)	25ft (7.62m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4250-509-YL	B-509	Yellow	4.250 (107.8)	25ft (7.62m)	1 roll (cont.)	B30-R10000 ✖



## ToughStripe® Printable Floor Marking Tape (B-483 with overlamine)

- Revolutionary new B-483 material has ultra aggressive adhesive
- Withstands forklift and pallet jack traffic without tearing or lifting
- Easy 3-step process: print label, position on floor, apply overlamine
- Each roll ships with a roll of clear overlamine which must be applied over printed label and onto appropriate surface for best performance

Service Temp: -40°F to 248°F  
Agency Approvals:



Figure 33

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP37,35	Fig. 33	B30C-1125-483BK-KT	B-483	White	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-1125-483BL-KT	B-483	White	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-1125-483GN-KT	B-483	White	3.000 (76.2)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-1125-483OR-KT	B-483	White	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-1125-483RD-KT	B-483	Yellow	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-1125-483WT-KT	B-483	Yellow	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-1125-483YL-KT	B-483	Yellow	3.000 (76.2)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-2250-483BK-KT	B-483	Yellow	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-2250-483BL-KT	B-483	Red	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-2250-483GN-KT	B-483	Red	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-2250-483OR-KT	B-483	Red	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-2250-483RD-KT	B-483	Blue	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-2250-483WT-KT	B-483	Blue	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-2250-483YL-KT	B-483	Blue	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-3000-483WT-KT	B-483	Green	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-3000-483YL-KT	B-483	Green	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-4000-483BL-KT	B-483	Green	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-4000-483BK-KT	B-483	Black	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-4000-483GN-KT	B-483	Black	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-4000-483OR-KT	B-483	Black	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R4400-WT
BBP37,35	Fig. 33	B30C-4000-483RD-KT	B-483	Orange	1.125 (28.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-4000-483WT-KT	B-483	Orange	2.250 (57.5)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000
BBP37,35	Fig. 33	B30C-4000-483YL-KT	B-483	Orange	4.000 (101.6)	100ft. (30.5m)	1 Roll (cont.)	B30-R6000



## Repositionable Vinyl (B-581)

- Aggressive adhesive stays in place but removes cleanly without leaving adhesive residue
- Ideal for temporary, removable and repositionable labels, such as 5S and lean inventory labels

Service temp: -40°F to 180°F Application temp: 50°F to 180°F  
Average Outdoor Durability: 5 years



Figure 33

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP37,35, 31, 33	Fig. 33	B30C-500-581-WT	B-581	White	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-581-WT	B-581	White	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-581-WT	B-581	White	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-581-WT	B-581	White	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-500-581-YL	B-581	Yellow	0.500 (12.7)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-1125-581-YL	B-581	Yellow	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-581-YL	B-581	Yellow	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-581-YL	B-581	Yellow	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂



## Retro Reflective Tape (B-584)

- Highly reflective material shines back brightly when struck by light
- Ideal for labeling outdoor utility pedestals, hard hats, jobsite equipment and roof-top equipment
- Recommended for low light or inclement weather conditions

Service Temp: -40°F to 158°F  
 Application Temp: 0°F to 158°F (yellow & orange), 50°F to 158°F (silver)  
 Average Outdoor Durability: 4 to 6 years




Figure 33

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP37,35, 31, 33	Fig. 33	B30C-1125-584-SL	B-584	Silver	1.125 (28.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-584-SL	B-584	Silver	2.250 (57.5)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-584-SL	B-584	Silver	4.000 (101.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-1125-584-YL	B-584	Yellow	1.125 (28.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-584-YL	B-584	Yellow	2.250 (57.5)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-584-YL	B-584	Yellow	4.000 (101.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-1125-584-OR	B-584	Orange	1.125 (28.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-584-OR	B-584	Orange	2.250 (57.5)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-584-OR	B-584	Orange	4.000 (101.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000 ✂



## BradyGlo™ High-Intensity Photoluminescent Tape (B-526)

- For glow-in-the-dark identification up to 10 hours
- Designed for directional and evacuation marking and equipment marking
- Ideal for marking emergency utility shut-offs, fire extinguishers, alarm pulls and vital equipment controls
- Complies with indoor use requirements specified in RS 6-1 and 6-1A of New York Local Law 26

Service Temp: -40°F to 140°F Application Temp: 40°F to 140°F




Figure 33

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP37,35, 31, 33	Fig. 33	B30C-1125-526	B-526	Luminous Green	1.125 (28.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-526	B-526	Luminous Green	2.250 (57.5)	50ft. (15.2m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-526	B-526	Luminous Green	4.000 (101.6)	50ft. (15.2m)	1 roll (cont.)	B30-R10000 ✂



## Cold Temperature Application Material (B-549)

- Special adhesive permanently adheres to extremely cold surfaces
- Can be applied in -10°F and lasts in -40°F
- Ideal for cold storage warehouses, coolers, freezers and short-term winter outdoor use

Service Temp: -40°F to 212°F Application Temp: -10°F to 212°F  
 Average Outdoor Durability: Up to 1 year




Figure 33

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Labels Per Roll	Rec. Ribbon
BBP37,35, 31, 33	Fig. 33	B30C-1125-549-WT	B-549	White	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-549-WT	B-549	White	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-549-WT	B-549	White	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂
BBP37,35, 31, 33	Fig. 33	B30C-1125-549-YL	B-549	Yellow	1.125 (28.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-2250-549-YL	B-549	Yellow	2.250 (57.5)	100ft. (30.5m)	1 roll (cont.)	B30-R10000
BBP37,35, 31, 33	Fig. 33	B30C-4000-549-YL	B-549	Yellow	4.000 (101.6)	100ft. (30.5m)	1 roll (cont.)	B30-R10000 ✂



## Circle Gauge Labels (B-595)

- Create circle gauge labels using the built in Circle Gauge App on the BBP®37 printer with white tape and multi-colored paneled ribbons
- Create labels to the specific diameter and range of values for your gauge - small or large gauges
- App allows you to create in-zone, out-of-zone, caution zone(s) or all three
- Multiple gauge labels can be printed/cut within a single ribbon panel to optimize ribbon usage
- Specify center hole size to facilitate accurate label placement and visibility of info that may be printed on your gauge



4" Continuous Tape

Paneled Ribbon

Gauge App on Printer

### Label Supply for Creating Circle Gauge Labels

Fits Printer Model(s)	Catalog #	Color	Size	
BBP37,35*	B30C-4000-595-WT	<input type="text"/>	White	4.0' x 100 ft. ✂

### Ribbons for Creating Circle Gauge Labels

Fits Printer Model(s)	Catalog #	Color	Size
BBP37,35	B30-R10000-GR-8		Green, Red Ribbon 8' panel length, 100 panel sets
BBP37,35	B30-R10000-KRYG-8		Black, Red, Yellow & Green Ribbon 8' panel length, 50 panel sets
BBP37,35	B30-R10000-KRBG-8		Black, Red, Blue and Green Ribbon 8' panel length, 50 panel sets

\* Supply fits BBP35, 37 for this application, fits BBP35, 37, 31, 33 for other applications. Cutting circular shape enabled on BBP37 model only.



## Gradient "Ruler" Labels (B-595)

- Create accurate scale or "ruler" labels using the built in Gradient Label App on the printer with continuous supplies
- Specify units in inches or millimeters, and choose from several interval tick mark options
- Include multiple colors on your label for multiple "zones"
- For scales longer than 7 feet (for example: labeling a lar tank) combine multiple strips and set start point on second label to start where first label left off



2.25" Continuous Tape

Gradient App on Printer

### Most Common Supplies for Making Gradient Ruler Labels (1 print color)

Fits Printer Model(s)	Catalog #	Color	Size	Description
BBP37,35*	B30C-4000-595-WT	<input type="text"/>	White	4.0' x 100 ft. for larger applications such as tank /vessel labeling ✂
BBP37,35*	B30C-2250-595-WT	<input type="text"/>	White	2.25' x 100 ft. for larger applications such as tank /vessel labeling
BBP37,35*	B30C-1125-595-WT	<input type="text"/>	White	1.125' x 100 ft. for smaller applications such as machinery labeling
BBP37,35*	B30C-500-595-WT	<input type="text"/>	White	0.50' x 100 ft. for smaller applications such as machinery labeling
BBP37,35*	B30C-4000-595-YL		Yellow	4.0' x 100 ft. for smaller applications such as machinery labeling ✂
BBP37,35*	B30C-2250-595-YL		Yellow	2.25' x 100 ft. for smaller applications such as machinery labeling
BBP37,35*	B30C-1125-595-YL		Yellow	1.125' x 100 ft. for smaller applications such as machinery labeling
BBP37,35*	B30C-500-595-YL		Yellow	0.50' x 100 ft. for smaller applications such as machinery labeling
BBP37,35*	B30-R10000		Black Ribbon	Continuous 200 ft.
BBP37,35*	B30-R10000-RD		Red Ribbon	Continuous 200 ft.

Other solid color tapes can be used with Black ribbon but those shown above are the most commonly used and offer highest visual contrast.

### Most Common Supplies for Making Gradient Ruler Labels (multiple print color zones)

Fits Printer Model(s)	Catalog #	Color	Size	Description
BBP37,35*	B30C-4000-595-WT	<input type="text"/>	White	4.0' x 100 ft. for larger applications such as tank /vessel labeling ✂
BBP37,35*	B30C-2250-595-WT	<input type="text"/>	White	2.25' x 100 ft. for larger applications such as tank /vessel labeling
BBP37,35*	B30C-1125-595-WT	<input type="text"/>	White	1.125' x 100 ft. for smaller applications such as machinery labeling
BBP37,35*	B30C-500-595-WT	<input type="text"/>	White	0.50' x 100 ft. for smaller applications such as machinery labeling
BBP37,35*	B30-R10000-KR-8		Black, Red Ribbon	8' panel length, 100 panel sets
BBP37,35	B30-R10000-KRGB-8		Black, Red, Green & Blue Ribbon	8' panel length, 50 panel sets
BBP37,35	B30-R10000-KRYG-8		Black, Red, Yellow & Green Ribbon	8' panel length, 50 panel sets

\* Supply fits BBP35, 37 for this application, fits BBP35, 37, 31, 33 for other applications.



## Arc Flash Labels (B-595)

- Create multi-color Arc Flash labels using pre-printed header supplies and the built in Arc Flash App on the BBP®35 and BBP®37 printers or Brady Workstation
- Simple app prompts you for text on each panel variable then automatically lays out the complete label
- Create labels with your panel's data in all black text or with red variables
- Pre-printed header supplies available with red ANSI Danger or orange ANSI Warning formats
- Printer can also print complete label on white continuous supply using multi-color paneled ribbons



### Supplies for creating Arc Flash Labels Using pre-printed headers

Fits Printer Model(s)	Catalog #	Color	Size	Description
BBP37,35	B30-25-595-ANSIWA	ANSI WARNING Header	4.0" x 6.0", 175 pcs	
BBP37,35	B30-241-595-ANSIWA	ANSI WARNING Header	2.25" x 3.0", 300 pcs	
BBP37,35	B30-25-595-ANSIDA	ANSI DANGER Header	4.0" x 6.0", 175 pcs	
BBP37,35	B30-241-595-ANSIDA	ANSI DANGER Header	2.25" x 3.0", 300 pcs	
BBP37,35*	B30-R10000	Black Ribbon	Continuous 200 ft.	For black text beneath header
BBP37,35	B30-R10000-KR-8	Black & Red Ribbon	8" panel length, 100 panel sets	For black text w/red variables beneath header

### Supplies for creating Arc Flash Labels Using White Continuous tape

Fits Printer Model(s)	Catalog #	Color	Size	Description
BBP37,35*	B30C-4000-595-WT	White		For 4" x 6" arc flash labels
BBP37,35*	B30C-2250-595-WT	White		For 2" x 3" arc flash labels
BBP37,35	B30-R10000-KO-8	Black & Orange Ribbon	8" panel length, 100 panel sets	For ANSI Warning header with black text
BBP37,35	B30-R10000-KRBO-8	Black, Red, Blue & Orange Ribbon	8" panel length, 50 panel sets	For ANSI Warning header with black or red text
BBP37,35	B30-R10000-KR-8	Black, Red	8" panel length, 100 panel sets	For ANSI Danger header with black text

\* Supply fits BBP35, 37 for this application, fits BBP35, 37, 31, 33 for other applications.



## Make Your Own Rigid Valve Tags

- Print labels on your Brady printer and apply them to these industrial-grade plastic tags
- Outdoor tag withstands temps -40°F to 180°F
- Die-cut (pre-cut) label supplies fit recessed area on tag



### Labels & Ribbon for Making Valve Tags

Catalog #	Color	Label Size	Labels per Roll
B30-219-595-BLNKWT	White	2.25" x 3.85"	250 pcs for LG tag
B30-242-595-BLNKWT	White	1.125" x 2.85"	300 pcs for SM tag
B30-R10000	Black	Continuous 200 ft.	Print Ribbon

### Tag Sizes

Description	Height Inch (mm)	Width Inch (mm)
Large Tag	2.500 (63.5)	4.000 (101.6)
Small Tag	1.500 (38.1)	3.000 (76.2)

Fits Printer Model(s)	Small Tag Catalog #	Large Tag Catalog #	Color
BBP37,35, 31, 33	41920	41921	Black
BBP37,35, 31, 33	41922	41923	Yellow
BBP37,35, 31, 33	41924	41925	Red
BBP37,35, 31, 33	41926	41927	Blue
BBP37,35, 31, 33	41928	41929	Green
BBP37,35, 31, 33	87694	87695	Orange
BBP37,35, 31, 33	87696	87697	White
BBP37,35, 31, 33	87698	87699	Gray
BBP37,35, 31, 33	87710	87711	Brown
BBP37,35, 31, 33	87712	87713	Tan
BBP37,35, 31, 33	142133		Variety Pack*

\* Variety Pack combines 30 tags including at least one of each size and color. Perfect for evaluating which sizes and colors you need.



## Blank Rigid Panels

- Create rigid labels and signs using adhesive output from your printer
- Ideal for labeling situations and surfaces where applying an adhesive label is difficult
- Panels are sized slightly larger than label output to facilitate centered and accurate placement of label on panel
- Labels can be hand-applied to panel or applied using a BLS1255 cold press laminator
- Panels are pre-drilled with holes in corners for mounting with screws or cable-ties
- Panels can also be mounted using foam tape or magnetic strips (available below)



BLS1255 Laminator



Double Sided  
Foam Tape Roll



Double Sided  
Foam Tape Strip



Magnet Strips

Catalog #	Material	Color	Sign Height Inch (mm)	Sign Length Inch (mm)	Qty
<b>Plastic Panels - rounded corners and hole punched</b>					
13620	Plastic	White	4.250 (107.9)	6.250 (158.8)	10
146074	Plastic	White	4.250 (107.9)	10.250 (260.4)	10
146075	Plastic	White	4.250 (107.9)	14.250 (361.9)	10
146076	Plastic	White	2.500 (63.5)	6.250 (158.8)	10
146077	Plastic	White	2.500 (63.5)	10.250 (260.4)	10
13621	Plastic	Yellow	4.250 (107.9)	6.250 (158.8)	10
146078	Plastic	Yellow	4.250 (107.9)	10.250 (260.4)	10
146079	Plastic	Yellow	4.250 (107.9)	14.250 (361.9)	10
146080	Plastic	Yellow	2.500 (63.5)	6.250 (158.8)	10
146081	Plastic	Yellow	2.500 (63.5)	10.250 (260.4)	10
<b>Aluminum Panels - rounded corners and hole punched</b>					
13629	Aluminum	White	4.250 (107.9)	6.250 (158.8)	10
106461	Aluminum	White	4.250 (107.9)	10.250 (260.4)	10
146082	Aluminum	White	4.250 (107.9)	14.250 (361.9)	10
146083	Aluminum	White	2.500 (63.5)	6.250 (158.8)	10
146113	Aluminum	White	2.500 (63.5)	10.250 (260.4)	10
13630	Aluminum	Yellow	4.250 (107.9)	6.250 (158.8)	10
146114	Aluminum	Yellow	4.250 (107.9)	10.250 (260.4)	10
146115	Aluminum	Yellow	4.250 (107.9)	14.250 (361.9)	10
146116	Aluminum	Yellow	2.500 (63.5)	6.250 (158.8)	10
146117	Aluminum	Yellow	2.500 (63.5)	10.250 (260.4)	10

Catalog #	Material	Size		Qty
<b>Laminator &amp; Panel Mounting Accessories</b>				
105038	BLS1255 Laminator			
78272	Double Sided Foam mounting tape (adhesive on both sides)	0.500 (12.7)	108 ft. (32.9m)	1 roll
78273	Double Sided Foam mounting tape (adhesive on both sides)	0.750 (19.1)	108 ft. (32.9m)	1 roll
97200	Double Sided Foam mounting tape strips (adhesive on both sides)	0.750 (19.1)	4.500 (114.3)	4 pcs
58301	Magnetic Strips (adhesive on one side, magnetic on other side)	1.000 (25.4)	4.000 (101.6)	10 pcs



### Creating a Rigid Sign or Label



1. Choose your rigid panel, select the needed material size and print your adhesive label



2. Peel away the first 1½" of liner from the label. Apply to rigid panel, aligning edge of label with edge of panel



3. Insert panel and rotate handle until first 1" of panel is "pinched." Then grasp liner and pull it away as you rotate the handle to move the panel through laminator




4. In less than 30 seconds you have a rigid sign ready to hang



## Product ID Materials

- A variety of polyester and specialty materials in wide format rolls designed for shape cutting multiple labels out of a single continuous roll
- Ideal for smaller volume custom shape cutting of Product ID and general industrial labels
- Proven materials with agency approvals for Product ID and asset tracking applications

<b>B-424:</b> Paper	Matte Bright White	Service temp: -40°F to 124°F	RoHS
<b>B-423:</b> Polyester w/standard adhesive	Gloss White	Service temp: -94°F to 248°F	RoHS
<b>B-432:</b> Polyester w/ stronger adhesive	Clear	Service temp: -40°F to 212°F	RoHS
<b>B-483:</b> Polyester w/ ultra-aggressive adhesive for rough surfaces	Gloss White	Service temp: -94°F to 248°F	RoHS
<b>B-484:</b> Polyester w/ ultra-aggressive adhesive and pliability for angular surfaces	Gloss White	Service temp: -40°F to 240°F	RoHS
<b>B-489:</b> Polyester w/ ultra-aggressive adhesive for rough surfaces	Matte White	Service temp: -94°F to 248°F	RoHS
<b>B-488:</b> Polyester w/ standard adhesive and chemical resistance	Matte White	Service temp: -40°F to 320°F	RoHS
<b>B-428:</b> Metallized Polyester w/standard adhesive for smooth surfaces	Matte Silver	Service temp: -40°F to 293°F	RoHS
<b>B-434:</b> Metallized Polyester w/stronger adhesive for textured surfaces	Gloss Silver	Service temp: -40°F to 194°F	RoHS
<b>B-486:</b> Metallized Polyester w/ultra-aggressive adhesive for rougher surfaces	Matte Silver	Service temp: -40°F to 248°F	RoHS
<b>B-565:</b> Metallized polyester w/ standard adhesive	Matte Silver	Service temp: -40°F to 240°F	RoHS
<b>B-595:</b> Indoor/Outdoor vinyl	Semi-Gloss White	Service temp: -40°F to 180°F	RoHS
<b>B-724:</b> Polyimide label for extremely high temperatures	Matte Amber	Service temp: -94°F to 518°F	RoHS
<b>B-727:</b> Polyimide label for standard temperatures	Gloss White	Service temp: -94°F to 212°F	RoHS
<b>B-437:</b> Tedlar® for high temp labeling & cable wraps		Service temp: -94°F to 275°F	RoHS
<b>B-787:</b> Polyvinyl flouride tape	Gloss White	Service temp: -94°F to 212°F	RoHS



Fits Printer Model(s)	Catalog #	Color	Size Inch (mm)	Length Feet (m)
BBP37,35	B30C-4000-424	White	4.000 (101.6)	150 ft. (45.7 m)
BBP37,35	B30C-4000-423	White	4.000 (101.6)	150 ft. (45.7 m)
BBP37,35	B30C-4000-432	Clear	4.000 (101.6)	120 ft. (36.6 m)
BBP37,35	B30C-4000-483	White	4.000 (101.6)	130 ft. (39.6 m)
BBP37,35	B30C-4000-484	White	4.000 (101.6)	150 ft. (45.7 m)
BBP37,35	B30C-4000-489	White	4.000 (101.6)	130 ft. (39.6 m)
BBP37,35	B30C-4000-488	White	4.000 (101.6)	130 ft. (39.6 m)
BBP37,35	B30C-4000-428	Silver	4.000 (101.6)	130 ft. (39.6 m)


Fits Printer Model(s)	Catalog #	Color	Size Inch (mm)	Length Feet (m)
BBP37,35	B30C-4000-434	Silver	4.000 (101.6)	130 ft. (39.6 m)
BBP37,35	B30C-4000-486	Silver	4.000 (101.6)	115 ft. (35.1 m)
BBP37,35	B30C-4000-437	White	4.000 (101.6)	150 ft. (45.7 m)
BBP37,35	B30C-4000-565	Silver	4.000 (101.6)	100 ft. (30.4 m)
BBP37,35	B30C-4000-595-WT	White	4.000 (101.6)	100 ft. (30.4 m)
BBP37,35	B30C-4000-724	Amber	4.000 (101.6)	130 ft. (39.6 m)
BBP37,35	B30C-4000-727	White	4.000 (101.6)	130 ft. (39.6 m)
BBP37,35	B30C-4000-787	White	4.000 (101.6)	60 ft. (18.3 m)

For recommended print ribbon refer to compatibility chart on page 20.




## Tamper-Evident Asset ID Labels (B-438)

- Leaves checkerboard footprint on surface and on label if removed to prevent re-use



Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP37,35, 31, 33	Fig. 2	B30-17-438	B-438	Matte Silver	2.000 (50.8)	1.000 (25.4)	2.500 (63.5)	1.125 (28.6)	1	1225	B30-R4300
BBP37,35, 31, 33	Fig. 2	B30-18-438	B-438	Matte Silver	3.000 (76.2)	1.000 (25.4)	3.250 (82.6)	1.250 (31.8)	1	1225	B30-R4300
BBP37,35, 31, 33	Fig. 2	B30-222-438	B-438	Matte Silver	3.000 (76.2)	2.000 (50.8)	3.250 (82.6)	2.250 (57.2)	1	650	B30-R4300
BBP37,35, 31, 33	Fig. 3	B30C-3000-438-SL	B-438	Matte Silver	3.000 (76.2)	100 ft. (30.5m)		3.250 (82.6)		1 roll (cont.)	B30-R4300



## Raised Profile Labels - Engraved Plate Substitutes - Rectangular Style (B-593)

Costs up to 80% less than engraved legend plates

- High gloss, polyester label with thick raised profile and ultra-aggressive adhesive (0.70mm thick)
- Ideal for inside-panel backer board labels and front-of-enclosure labeling
- Up to 80% less than engraved plates and print out in about 4 seconds
- 10-year outdoor durability rating
- 6 colors, 7 rectangular sizes

Service Temp: -4°F to 212°F Application Temp: 50°F to 212°F  
 Average Outdoor Durability: Up to 10 years  
 Agency Approvals:




Figure 18c

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Height A Inch (mm)	Label Width B Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP37,35,31,33	Fig. 18c	B30EP-171-593-WT	B-593	White	0.490 (12.5)	1.060 (26.9)	0.750 (19.1)	1.375 (34.9)	1	500	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-172-593-WT	B-593	White	0.590 (15.0)	1.770 (45.0)	0.850 (21.6)	2.500 (63.5)	1	450	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-175-593-WT	B-593	White	0.750 (19.1)	3.000 (76.2)	1.000 (25.4)	3.250 (82.6)	1	375	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-173-593-WT	B-593	White	1.000 (25.4)	2.000 (50.8)	1.250 (31.8)	2.500 (63.5)	1	300	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-174-593-WT	B-593	White	1.000 (25.4)	4.000 (101.6)	1.250 (31.8)	4.250 (108.0)	1	300	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-176-593-WT	B-593	White	1.000 (25.4)	3.000 (76.2)	1.250 (31.8)	3.250 (82.6)	1	300	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-177-593-WT	B-593	White	2.500 (63.5)	3.000 (76.2)	2.750 (69.9)	3.250 (82.6)	1	125	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-171-593-YL	B-593	Yellow	0.490 (12.5)	1.060 (26.9)	0.750 (19.1)	1.375 (34.9)	1	500	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-172-593-YL	B-593	Yellow	0.590 (15.0)	1.770 (45.0)	0.850 (21.6)	2.500 (63.5)	1	450	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-173-593-YL	B-593	Yellow	0.750 (19.1)	3.000 (76.2)	1.000 (25.4)	3.250 (82.6)	1	375	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-173-593-YL	B-593	Yellow	1.000 (25.4)	2.000 (50.8)	1.250 (31.8)	2.500 (63.5)	1	300	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-174-593-YL	B-593	Yellow	1.000 (25.4)	4.000 (101.6)	1.250 (31.8)	4.250 (108.0)	1	300	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-176-593-YL	B-593	Yellow	1.000 (25.4)	3.000 (76.2)	1.250 (31.8)	3.250 (82.6)	1	300	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-177-593-YL	B-593	Yellow	2.500 (63.5)	3.000 (76.2)	2.750 (69.9)	3.250 (82.6)	1	125	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-171-593-BK	B-593	Black	0.490 (12.5)	1.060 (26.9)	0.750 (19.1)	1.375 (34.9)	1	500	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-172-593-BK	B-593	Black	0.590 (15.0)	1.770 (45.0)	0.850 (21.6)	2.500 (63.5)	1	450	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-175-593-BK	B-593	Black	0.750 (19.1)	3.000 (76.2)	1.000 (25.4)	3.250 (82.6)	1	375	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-173-593-BK	B-593	Black	1.000 (25.4)	2.000 (50.8)	1.250 (31.8)	2.500 (63.5)	1	300	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-174-593-BK	B-593	Black	1.000 (25.4)	4.000 (101.6)	1.250 (31.8)	4.250 (108.0)	1	300	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-176-593-BK	B-593	Black	1.000 (25.4)	3.000 (76.2)	1.250 (31.8)	3.250 (82.6)	1	300	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-177-593-BK	B-593	Black	2.500 (63.5)	3.000 (76.2)	2.750 (69.9)	3.250 (82.6)	1	125	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-171-593-GN	B-593	Green	0.490 (12.5)	1.060 (26.9)	0.750 (19.1)	1.375 (34.9)	1	500	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-172-593-GN	B-593	Green	0.590 (15.0)	1.770 (45.0)	0.850 (21.6)	2.500 (63.5)	1	450	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-175-593-GN	B-593	Green	0.750 (19.1)	3.000 (76.2)	1.000 (25.4)	3.250 (82.6)	1	375	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-173-593-GN	B-593	Green	1.000 (25.4)	2.000 (50.8)	1.250 (31.8)	2.500 (63.5)	1	300	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-174-593-GN	B-593	Green	1.000 (25.4)	4.000 (101.6)	1.250 (31.8)	4.250 (108.0)	1	300	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-176-593-GN	B-593	Green	1.000 (25.4)	3.000 (76.2)	1.250 (31.8)	3.250 (82.6)	1	300	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-177-593-GN	B-593	Green	2.500 (63.5)	3.000 (76.2)	2.750 (69.9)	3.250 (82.6)	1	125	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-171-593-RD	B-593	Red	0.490 (12.5)	1.060 (26.9)	0.750 (19.1)	1.375 (34.9)	1	500	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-172-593-RD	B-593	Red	0.590 (15.0)	1.770 (45.0)	0.850 (21.6)	2.500 (63.5)	1	450	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-173-593-RD	B-593	Red	1.000 (25.4)	2.000 (50.8)	1.250 (31.8)	2.500 (63.5)	1	300	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-174-593-RD	B-593	Red	1.000 (25.4)	4.000 (101.6)	1.250 (31.8)	4.250 (108.0)	1	300	B30-R4400-WT
BBP37,35,31,33	Fig. 18c	B30EP-171-593-SL	B-593	Silver	0.490 (12.5)	1.060 (26.9)	0.750 (19.1)	1.375 (34.9)	1	500	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-172-593-SL	B-593	Silver	0.590 (15.0)	1.770 (45.0)	0.850 (21.6)	2.500 (63.5)	1	450	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-173-593-SL	B-593	Silver	1.000 (25.4)	2.000 (50.8)	1.250 (31.8)	2.500 (63.5)	1	300	B30-R6000
BBP37,35,31,33	Fig. 18c	B30EP-174-593-SL	B-593	Silver	1.000 (25.4)	4.000 (101.6)	1.250 (31.8)	4.250 (108.0)	1	300	B30-R6000

U.S. Patent Nos. US8475914B2; US9005729B2.





## Raised Profile Labels - Engraved Plate Substitutes - Push Button Style (B-593)

Costs up to 80% less than engraved legend plates

- High gloss, polyester label with thick raised profile and ultra-aggressive adhesive (0.70mm thick)
- High performance, low cost substitute to engraved plates
- 10-year outdoor durability rating
- On-demand labeling: labels print out in less than 4 seconds
- 5 push button sizes (including keyed and non-keyed 22.5mm, and 30.5mm hole diameter keyed)

Service Temp: -4°F to 212°F  
 Application Temp: 50°F to 212°F  
 Average Outdoor Durability: Up to 10 years  
 Agency Approvals:




Figure 18b  
(Without key hole)




Figure 18a

Fits Printer Model(s)	Diagram	Catalog #	B#	Color	Label Height A Inch (mm)	Label Width B Inch (mm)	Hole Diameter C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP37,35, 31, 33	Fig. 18a	B30EP-167-593-WT	B-593	White	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R6000
BBP37,35, 31, 33	Fig. 18b	B30EP-167U-593-WT	B-593	White	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R6000
BBP37,35, 31, 33	Fig. 18a	B30EP-169-593-WT	B-593	White	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R6000
BBP37,35, 31, 33	Fig. 18a	B30EP-168-593-WT	B-593	White	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R6000
BBP37,35, 31, 33	Fig. 18a	B30EP-170-593-WT	B-593	White	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R6000
BBP37,35, 31, 33	Fig. 18a	B30EP-167-593-YL	B-593	Yellow	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R6000
BBP37,35, 31, 33	Fig. 18b	B30EP-167U-593-YL	B-593	Yellow	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R6000
BBP37,35, 31, 33	Fig. 18a	B30EP-169-593-YL	B-593	Yellow	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R6000
BBP37,35, 31, 33	Fig. 18a	B30EP-168-593-YL	B-593	Yellow	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R6000
BBP37,35, 31, 33	Fig. 18a	B30EP-170-593-YL	B-593	Yellow	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R6000
BBP37,35, 31, 33	Fig. 18a	B30EP-167-593-BK	B-593	Black	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18b	B30EP-167U-593-BK	B-593	Black	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-169-593-BK	B-593	Black	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-168-593-BK	B-593	Black	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-170-593-BK	B-593	Black	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-167-593-GN	B-593	Green	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18b	B30EP-167U-593-GN	B-593	Green	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-169-593-GN	B-593	Green	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-168-593-GN	B-593	Green	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-170-593-GN	B-593	Green	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-167-593-RD	B-593	Red	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18b	B30EP-167U-593-RD	B-593	Red	1.500 (38.1)	1.200 (30.5)	0.885 (22.5)	1.750 (44.5)	2.500 (63.5)	1	200	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-169-593-RD	B-593	Red	1.800 (45.7)	1.800 (45.7)	1.200 (30.5)	2.000 (50.8)	2.500 (63.5)	1	190	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-168-593-RD	B-593	Red	1.900 (48.3)	1.200 (30.5)	0.885 (22.5)	2.125 (54.0)	2.500 (63.5)	1	180	B30-R4400-WT
BBP37,35, 31, 33	Fig. 18a	B30EP-170-593-RD	B-593	Red	2.400 (60.9)	2.400 (60.9)	1.200 (30.5)	2.625 (66.7)	3.250 (82.6)	1	145	B30-R4400-WT

U.S. Patent Nos. US8475914B2; US9005729B2.



### Calculate Your Cost Savings

A 1" x 2" rectangular raised profile label costs approximately **\$0.60**, lasts up to 10 years outdoors and prints in seconds!  
 A 22.5mm push button label will cost you about **\$0.32!**

What are you paying for engraved plates?



## SUPPLY STARTER KITS

Get started right and save a little too with a Brady supply starter kit! Packages of most commonly used labels and ribbons for the most common labeling applications. Just enough supplies to ensure you have what you need to get going on that project.



### Basic Supply Starter Kit - Small

- (1) 4" Yellow Vinyl (B30C-4000-595-YL)
- (1) 4" White Vinyl (B30C-4000-595-WT)
- (1) 2.25" Red Vinyl (B30C-2250-595-RD)
- (1) Black Print Ribbon (B30-R10000)
- (1) White Print Ribbon (B30-R10000-WT)

Printer sold separately

Catalog #	Description
146069	Basic Supply Starter Kit - Small



### Gauge Label Supply Kit - Small

- (2) 4" White Vinyl (B30C-4000-595-WT)
- (2) Green & Red Pannelled Print Ribbon - 8" Panel length (B30-R10000-GR-8)

Printer sold separately. BBP35 or 37 models needed to use these supplies

Catalog #	Description
146070	Gauge Label Supply Kit - Small



### Arc Flash Supply Kit - Small

- (2) 4 x 6 ANSI Warning Header Roll (B30-25-595-ANSIWA)
- (1) Black Print Ribbon (B30-R10000)

Printer sold separately

Catalog #	Description
142061	Arc Flash Warning Supply Kit - Large
146071	Arc Flash Warning Supply Kit - Small

### Arc Flash Supply Kit - Large

- (2) 4" x 6" B-595 ANSI Warning Header (B30-25-595-ANSIWA)
- (1) 2.25" x 3" B-595 ANSI Warning Header (B30-241-595-ANSIWA)
- (1) 1" x 4" B-593 White Raised Panel Label (B30EP-174-593-WT)
- (1) 2.25" B-595 Orange Vinyl (B30C-2250-595-OR)
- (3) Black Print Ribbon (B30-R10000)

Printer sold separately



### GHS Supply Kit - Small

- (2) 4 x 6" GHS label w/L4B four-diamond layout (B30-262-7569-CLP4B)
- (1) Black Print Ribbon (B30-R10000)

Printer sold separately

Catalog #	Description
146072	GHS Supply Kit - Large
146073	GHS Supply Kit - Small

### GHS Supply Kit - Large

- (1) 4 x 6" GHS label w/L4B four-diamond layout (B30-262-7569-CLP4B)
- (2) 3 x 4" GHS label w/L4B four-diamond layout (B30-261-7569-CLP4B)
- (1) 2 x 3" GHS label w/L4B four-diamond layout (B30-260-7569-CLP4B)
- (3) Black Print Ribbon (B30-R10000)

Printer sold separately



### Safety & Compliance Supply Kit - Large

- (1) 4" x 6" B-595 ANSI Danger Header (B30-25-595-ANSIDA)
- (1) 4" x 6" B-595 ANSI Warning Header (B30-25-595-ANSIWA)
- (1) 4" x 6" B-595 ANSI Caution Header (B30-25-595-ANSICA)
- (1) 4" x 6" B-595 ANSI Notice Header (B30-25-595-ANSINO)
- (1) 4" B-526 Photoluminescent (B30C-4000-526)
- (1) 4" x 6" B-595 RTK NFPA (B30-263-595-NFPA)
- (2) Black Print Ribbon (B30-R10000)
- (1) Red Print Ribbon (B30-R10000-RD)

Printer sold separately

Catalog #	Description
142062	Safety & Compliance Supply Kit - Large



### 5S Visual Workplace Supply Kit - Large

- (1) 4" B-595 White Vinyl (B30C-4000-595-WT)
- (1) 2.25" B-595 White Vinyl (B30C-2250-595-WT)
- (1) 4" B-595 Yellow Vinyl (B30C-4000-595-YL)
- (1) 2.25" B-595 Yellow Vinyl (B30C-2250-595-YL)
- (1) 2.25" B-581 Repositionable Vinyl (B30C-2250-581-WT)
- (1) 1.125" B-581 Repositionable Vinyl (B30C-1125-581-WT)
- (1) 2.5" Magnetic Vinyl (B30C-2500-509-WT)
- (1) Blank Valve Tag Variety Pack (142133)
- (1) Die Cut Labels for Valve Tags (B30-219-595-BLNKWT)
- (1) 4" x 6" B-595 Caution Header (B30-25-595-ANSIWA)
- (2) Black Print Ribbon (B30-R10000)
- (1) Red Print Ribbon (B30-R10000-RD)
- (1) Green Print Ribbon (B30-R10000-GN)
- (1) Blue Print Ribbon (B30-R10000-BL)

Printer sold separately

Catalog #	Description
142063	5S Visual Workplace Supply Kit - Large



### Pipe Identification Supply Kit - Large

- (1) 4" B-595 Yellow Vinyl (B30C-4000-595-YL)
- (1) 2.25" B-595 Yellow Vinyl (B30C-2250-595-YL)
- (1) 1.125" B-595 Yellow Vinyl (B30C-1125-595-YL)
- (1) 4" B-595 Green Vinyl (B30C-4000-595-GN)
- (1) 2.25" B-595 Green Vinyl (B30C-2250-595-GN)
- (1) 1.125" B-595 Green Vinyl (B30C-1125-595-GN)
- (1) 1.125" B-595 Blue Vinyl (B30C-1125-595-BL)
- (1) 2.25" B-595 Red Vinyl (B30C-2250-595-RD)
- (1) 1.125" B-595 Red Vinyl (B30C-1125-595-RD)
- (1) 1" x 4" B-593 Black Raised Panel (B30EP-174-593-BK)
- (1) Blank Valve Tag Variety Pack (142133)
- (1) Small Die Cut Labels for Valve Tags (B30-242-595-BLNKWT)
- (3) Black Print Ribbon (B30-R10000)
- (2) White Print Ribbon (B30-R10000-WT)

Printer sold separately

Catalog #	Description
142064	Pipe ID Supply Kit - Large



### General Industrial & 5S Supply Kit - Large

- (1) 4" B-595 White (B30C-4000-595-WT)
- (1) 2.25" B-595 White (B30C-2250-595-WT)
- (1) 1.125" B-595 White Vinyl (B30C-1125-595-WT)
- (1) 4" B-595 Yellow Vinyl (B30C-4000-595-YL)
- (1) 2.25" B-595 Yellow Vinyl (B30C-2250-595-YL)
- (1) 1.125" B-595 Yellow Vinyl (B30C-1125-595-YL)
- (1) 2.5" x 3" B-593 Black Raised Panel (B30EP-177-593-BK)
- (1) 4" x 6" B-595 ANSI Danger Header (B30-25-595-ANSIDA)
- (1) 4" x 6" B-595 ANSI Caution Header (B30-25-595-ANSICA)
- (1) 2.25" Reflective Yellow (B30C-2250-584-YL)
- (1) 4.25" White Tag Stock (B30C-4250-551-WT)
- (2) Black Print Ribbon (B30-R10000)
- (1) White Print Ribbon (B30-R10000-WT)
- (1) Red Print Ribbon (B30-R10000-RD)

Printer sold separately

Catalog #	Description
142065	General Industrial & 5S Supply Kit - Large



## Industrial Grade Print Ribbons

### “Drop & Click” print ribbons for 5 second ribbon supply changes

- Tough, smear-proof ribbons that produce long-lasting printed text and can withstand years in industrial areas and outdoor conditions
- Self-contained cartridges drop straight into printer with a “click”
- No calibrating, no threading, no wasted feeding, no hassles and the ink will always be facing the right direction!
- Printer notifies user if installed ribbon is not recommended for installed labels

Ribbon installs in 5 seconds...  
snaps into place!

### BBP®35 & BBP®37 Print Ribbon / Material Compatibility

B-# Material		B30-R4300 (Black)	B30-R6000 (Black)	B30-R6200 (Black)	B30-R10000 (Black)	B30-R10000-WT (White)	B30-R4400-WT (White)	B30-R10000-YL (Yellow)	B30-R10000-YL2 (Yellow)	B30-R10000 (Colors)
B-423	Glossy White Polyester	-	●	●	-	-	-	-	-	-
B-424	Matte White Paper	●	-	-	-	-	-	-	-	-
B-428	Metallized Polyester	●	-	-	-	-	-	-	-	-
B-432	Glossy Clear Polyester	-	●	-	-	-	●	-	-	-
B-434	Glossy Metallized Polyester	-	●	-	-	-	-	-	-	-
B-437	Tedlar®	●	-	-	-	-	-	-	-	-
B-438	Tamper Evident Metallized Polyester	●	-	-	-	-	-	-	-	-
B-483	Glossy White Polyester	-	●	-	-	-	-	-	-	-
B-483	ToughStripe®	-	●	-	-	-	●	-	-	-
B-484	Glossy White Polyester	-	●	-	-	-	-	-	-	-
B-486	Matte Metallized Polyester	●	-	-	-	-	-	-	-	-
B-488	Matte White Polyester	●	-	-	-	-	-	-	-	-
B-489	Matte White Polyester	●	-	-	-	-	-	-	-	-
B-509	Printable Magnetic	-	-	-	●	-	-	-	-	● **
B-526	Photoluminescent Polyester	-	-	-	●	-	-	-	-	● **
B-549	Cold Temp Polyester	-	-	-	●	●	-	-	-	● **
B-551	Non-Adhesive Tag	-	-	-	●	-	-	-	-	● **
B-565	Metallized Polyester	-	-	-	●	-	-	-	-	-
B-569	Low-Halide Polyester	-	-	-	●	●	-	-	-	● **
B-581	Repositionable Vinyl	-	-	-	●	●	-	-	-	● **
B-584	Retro Reflective	-	-	-	●	-	-	-	-	● **
B-593	Raised Panel Engraved Plate Substitute	-	●	-	-	-	●	-	-	-
B-595	Outdoor Vinyl	-	-	-	●	●	-	● ***	● ***	● **
B-854	Toughwash™ Metal Detectable	-	●	-	-	-	-	-	-	-
B-855	Toughwash™	-	●	-	-	-	-	-	-	-
B-724	Matte Amber Polyimide	●	-	-	-	-	-	-	-	-
B-727	Glossy White Polyimide	-	●	-	-	-	-	-	-	-
B-787	Glossy White Polyvinyl Fluoride	-	●	-	-	-	-	-	-	-
B-7569	Vinyl Film	-	-	-	●	-	-	-	-	-

Refer to the corresponding Tech Data Sheets for complete material information at [BradyID.com/techdata](http://BradyID.com/techdata).

\*\*Colored ribbons optimized for use on white material. Test use on other material colors for suitability to your application.

\*\*\*For printing yellow onto white B-595 use B30-R10000-YL. For printing yellow onto other colors of B-595 use B30-R10000-YL2.




## Single Color Print Ribbons

- Solid color ribbons for printing a single color onto a label
- Can be swapped out for printing multi-color labels on BBP35 or BBP37 printer if a paneled multi-color ribbon is not on-hand

Fits Printer Model(s)	Catalog #	Color	Size Inch (mm)	Length Feet (m)
BBP37,35,31,33	B30-R10000	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-WT	White	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R4400-WT	White	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R4300	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R6000	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R6200	Black	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-RD	Red	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-GN	Green	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-BL	Blue	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-YL	Yellow*	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-YL2	Yellow*	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-OR	Orange	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-MA	Magenta	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-PRCCY	Process Cyan**	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-PRCYEL	Process Yellow**	4.330 (109.9)	200 ft. (60.9 m)
BBP37,35,31,33	B30-R10000-PRCMAG	Process Magenta**	4.330 (109.9)	200 ft. (60.9 m)

\* For printing yellow onto white B-595 use B30-R10000-YL. For printing yellow onto other colors of B-595 use B30-R10000-YL2.

\*\* Process ribbons print a much lighter shade - designed to be used together with other process ribbons and black ribbon to lay down a dot pattern for printing "blended" colors and process color objects.



## Multi-Color "Paneled" Print Ribbons

- Ribbons have panels of 2- or 4-different colors for printing multiple colors onto a label
- Use CMYK ribbon for printing blended colors. Blended colors are not as saturated as solid or spot color paneled ribbons, but do offer a broader palette of available colors and shades
- Print multiple colors without having to swap in multiple ribbons

### Two Color Print Ribbons

Fits Printer Model(s)	Catalog #	Color	Size Inch (mm)	Length Feet (m)
<b>8" panel length - Typical yield: 100 panel sets per roll</b>				
BBP37,35	B30-R10000-KR-8	Black and Red	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KY-8	Black and Yellow	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KB-8	Black and Blue	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KO-8	Black and Orange	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KG-8	Black and Green	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-GR-8	Green and Red	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
<b>16" panel length - Typical yield: 60 panel sets per roll</b>				
BBP37,35	B30-R10000-KR-16	Black and Red	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KY-16	Black and Yellow	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KB-16	Black and Blue	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KO-16	Black and Orange	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KG-16	Black and Green	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-RB-16	Red and Blue	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)

### Four Color Print Ribbons

Fits Printer Model(s)	Catalog #	Color	Size Inch (mm)	Length Feet (m)
<b>8" panel length - Typical yield: 50 panel sets per roll</b>				
BBP37,35	B30-R10000-KRGB-8	Black, Red, Green and Blue	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KRYG-8	Black, Red, Yellow and Green	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KRYB-8	Black, Red, Yellow and Blue	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KRBO-8	Black, Red, Blue and Orange	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-CMYK-8	Process Cyan, Mgnta, Yell, Blk	4.330 (101.9) x 8.000 (203.2) Panels	200 ft. (60.9 m)
<b>16" panel length - Typical yield: 30 panel sets per roll</b>				
BBP37,35	B30-R10000-KRGB-16	Black, Red, Green and Blue	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-KRYB-16	Black, Red, Yellow and Blue	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)
BBP37,35	B30-R10000-CMYK-16	Black, Cyan, Magenta, Yellow **	4.330 (101.9) x 16.000 (406.4) Panels	200 ft. (60.9 m)

\*\* Process ribbons print a much lighter shade - designed to be used together with other process ribbons and black ribbon to lay down a dot pattern for printing "blended" colors and process color objects.

## BRADY WORKSTATION

**Create labels on your PC and send to your printer.** Brady has revolutionized the way you create labels on your PC with the new Brady Workstation and its apps that are specific to the projects you want to execute. It's built to be super powerful and super simple – just pick the apps you need to get your job done.

**How does it work?** Download the free Brady Workstation program then fill it with the apps you need and leave out the ones you don't.

**Apps made to work for you.** These apps feature built in regulations and standards, pictograms, common phrases, data importing, guidance and help functions — all to help you create signs and labels to keep your facility compliant and safe. Most of the apps are free, while others vary in cost with the option of a 14-day free trial.



## AVAILABLE BRADY WORKSTATION APPS

There are several label creation apps within Brady Workstation to fit a wide variety of applications. Don't need all of the apps? No problem! Once Brady Workstation is downloaded to your PC, you can choose which apps you want and leave out the ones you don't.



### Custom Designer App

Design anything you can imagine in this free app. Start with a blank canvas to create a label or sign that meets your unique needs. Add barcodes or QR codes, import data from Excel and more!



### Pipe Marker & Arrow Tape Apps

Easily comply with the latest pipe marking standard, ANSI/ASME 13.1 2007 or choose a different standard if you wish. This free app allows you to create customized pipe markers, then save them to use again whenever you want more.



### Express Signs App

Create your signs in no time with this free app. Simply pick a template, enter your info and you're ready to print! Don't like the layouts? Adjust them.



### Lockout Writer App

Quickly create compliant lockout tagout labels. This app includes procedure printing templates, simple translations, easy-to-use image editing for callouts, and import capabilities from Lockout-Pro™ software.



### GHS Labels App

Creating GHS labels is now amazingly simple. Enter your SDS data one time in simple drop down list and template text entry fashion, and you can create any size label and print it at any time.



### Download Workstation Today!

Visit [workstation.bradyid.com](http://workstation.bradyid.com) to download the program and choose from several apps, including Express Signs app, Pipe Marker app, Custom Designer app, GHS app and Lockout Writer app.



1. Download Brady Workstation at [www.bradyid.com.sg/workstation](http://www.bradyid.com.sg/workstation)
2. Fill the workstation with the apps you want and leave out the ones you don't
3. Save time by quickly designing labels within the app and then printing them on your BBP®31, BBP®33, BBP®35, BBP®37 and BBP®85 printers

## Printer Specifications

Multi-color label printers with unprecedented capabilities, unrivaled ease of use and the best materials. There's never been a better tool to label your entire facility.

BBP®35 Printer and BBP®37 Printer			
Description	Facility, Safety and Lean 5S printer for walk up and print ease of use, fast supply changeovers, multicolor printing and ability to cut-out text and shapes (cut-outs enabled on BBP37 only). Best choice for "lean event" labeling situations and multiple user locations because it has a very approachable interface and very fast supply changeovers.		
Applications	Facility & Safety ID, Signs, Pipe Markers, Lean/5S, Arc Flash Labels, GHS & Chemical Labels, Equipment Labels, Panel & Push Button Labels, Reflective & Glow in the Dark Labels, Tags, Magnetic, Cold-Temp Labeling. Cut-out Text with BBP37 only.		
Label Material Types	Extremely aggressive 8-10 year outdoor vinyl with high tack and chemical resistance, plus Toughstripe® floor tape, wash-down material, 10-hr glow in the dark, reflective, magnetic, tags, engraved plate substitute and 20 other materials.		
Includes	Printer, Power Cord, USB Cable, Cleaning Kit, Cutter Cleaning Tool, Quick Start Guide		
Warranty	5 year		
<b>Printer Features:</b>			
Print Resolution	300 dpi		
Color Printing Capability	Multi Color		
Maximum Print Speed	5 in/sec		
Cutter Type	Auto Cutter. BBP37 also has XY Cutter.		
Media Sensor Adjustment	None		
<b>Display &amp; User Interface:</b>			
Display Type	Color Touch Screen		
Display Size	3.63 in x 6.0 in		
Keyboard Type	Full Size QWERTY		
Supply Remaining Gauge	Yes		
Languages	English, Spanish, Portuguese, French		
Units	Inches, millimeters, points		
<b>Stand-Alone Apps &amp; Editing:</b>			
Built-In Label Wizards	Custom Label	Gradient Scale	
	GHS / CLP	Right-To-Know	
Built-In Label Wizards	Safety Signs	WHMIS	
	Pipe Marker	Tags	
	Arc Flash	General Templates	
	Circle Gauge	Quick Label	
<b>Fonts / Graphics / Symbologies:</b>			
Font Sizes	0.05 in - 3.5 in		
Font Styles	Arial, Arial 65, Courier New, Tahoma, Times New Roman plus more with Brady Workstation. Can also import TrueType fonts to printer		
Symbols Quantity	664		
Symbols Categories	Arrows	Miscellaneous	
	Fire Safety	Packaging	
Barcode Symbologies - Linear	First Aid/Rescue	Personal Protective Equipment	
	Hazardous Transport	Prohibition	
	Hazmat GHS/CLP	Shapes	
	Hazmat HSID	Sign Headers	
	Imported Graphics	Warning	
	ISO Graphics	WHMIS	
	Mandatory		
	Code 39	Additional through	
	Code 128 Auto	Brady Workstation	
	Interleaved 2 of 5		
Barcode Symbologies - 2D	QR Code	Additional through	
	PDF417	Brady Workstation	
<b>Media / Supplies Information:</b>			
Compatible Media	B30 Series (manufactured after September 1, 2015)		
Compatible Ribbons	B30 Series (manufactured after September 1, 2015)		
Die Cuts vs Continuous	Continuous Tapes, Pre-Printed Die Cut Labels, General Die Cut Labels		
Ribbon & Label Installation	<b>Media:</b> Supplied in cartridge, drops into place, 15 sec changeover		
	<b>Ribbon:</b> Supplied in cartridge, snaps into place, 5 sec changeover		
Custom Media Parts Available	No		
Media Widths	0.5 to 4 in		


Compatible Brady Material Numbers	B-423, B-424, B-428, B-432, B-434, B-437, B-438, B-483, B-484, B-486, B-488, B-489, B-489, B-509, B-526, B-549, B-551, B-565, B-569, B-581, B-584, B-593, B-595, B-724, B-727, B-787, B854, B-855, B-7569
<b>Software &amp; Connectivity:</b>	
Connectivity Options	Stand-alone use, Ethernet, USB
Software Compatibility	Brady Workstation
<b>Physical / Operational Characteristics:</b>	
Dimensions	11 in H x 19 in W x 14.25 in D
Weight	36 LB
Operating Temperature Range	50° to 104° F
Storage Temperature Range	-4° to 122° F
Operating Humidity Range	20%-80% RH Non- Condensing
Storage Humidity Range	15% to 90% RH Non- Condensing
Power Supply Voltage	110V - 240V
Auto Shutoff / Power Conserve	Yes
<b>Agency Approvals / Regulatory Compliance:</b>	
Enables Industry Compliance	USA & Canada - cULc
	Europe - CE (including Eu RoHS)
	Argentina - UL-AR and S Mark
	Mexico - UL NOM CoC
	Australia - RCM mark
	Russia - EAC
	Korea - KC
	China - CCC and RoHS
	India - BIS
	Taiwan - BSMI Exemption
South Africa - LOA and SABS (No logo on product label)	
U.S. Patents	Multiple U.S. Patents Apply Printers: 6364552 B1; 6788324; 6768502 B2 BBP®37 Printer Only: 6664995 B2; Ribbon cartridges: 6860658 B2; D480749
MSDS	n/a



### Transfer Tape is the Best Way to Apply Cut-Out Shapes & Text!

Transfer Tape Catalog #76737 (4.25" x 200 ft. roll)

1. Cut out your shape or text and weed away unneeded material
2. Apply transfer tape over your cut-out objects and press firmly
3. Peel back transfer tape which will lift and expose the adhesive side of your now pre-spaced objects
4. Position object in place and press firmly onto final surface
5. Peel back transfer tape at sharp angle to surface
6. Works great for cut-out text on rigid sign panels too





## BBP<sup>®</sup>37

COLOR & CUT  
SIGN & LABEL PRINTER

## BBP<sup>®</sup>35

MULTICOLOR SIGN & LABEL PRINTER

When you need to create a safer, leaner and more productive workplace by communicating hazards, procedures and facility information at-a-glance – you need the power of a BBP<sup>®</sup>35 or BBP<sup>®</sup>37 sign and label printer. With multi-color printing, shape-cutting capabilities and fast printing, you can color your way to an improved workplace by creating effective visuals right when you need them.

### Printers

Catalog #	Description
BBP35	BBP35 Multicolor Sign & Label Printer
BBP37	BBP37 Color & Cut Sign & Label Printer

### Brady Workstation

Visit [workstation.bradynid.com](http://workstation.bradynid.com)

Catalog #	Description
Free Download	Brady Workstation Program
BWRK-GHS-DWN	GHS Labels app for Brady Workstation (download)
BWRK-LOW-DWN	Lockout Writer app for Brady Workstation (download)
Free Download	Custom Designer app for Brady Workstation
Free Download	Express Signs app for Brady Workstation
Free Download	Pipe Marker app for Brady Workstation
Free Download	Arrow Tape app for Brady Workstation
Free Download	Arc Flash app for Brady Workstation

Check [workstation.bradynid.com](http://workstation.bradynid.com) for up-to-date apps.

### Printer Accessories

Catalog #	Description
120994	Rolling case with handle, 2 pockets for supplies
B31-WIPER	5 pack of extra media wipers
PCK-6	Cleaning swabs that are pre-soaked in IPA (50 per pack)
76737	Transfer tape for cut-out objects (200 ft. roll)
BBP37-BLADE	Replacement XY cutting blade (1 each)

## CONTACT US

Brady's global presence makes it easy for you to do business with us wherever you are. To find out more about Brady and our products, please visit us at [www.bradynid.com.sg](http://www.bradynid.com.sg) or email us at [ContactUs\\_SA@bradycorp.com](mailto:ContactUs_SA@bradycorp.com).

### APAC Offices

#### AUSTRALIA

Telephone: (612) 8717 6300

#### CHINA

Telephone: (86) 21 6100 6588

#### HONG KONG

Telephone: (852) 2216 9283

#### INDIA

Telephone: (91) 80 66582 900

#### INDONESIA

Telephone: (65) 6477 7261

#### JAPAN

Telephone: (81) 042 655 2535

#### MALAYSIA

Telephone: (60) 4 810 1688

#### PHILIPPINES

Telephone: (65) 6477 7261

#### SINGAPORE

Telephone: (65) 6477 7261

#### SOUTH KOREA

Telephone: (02) 2192 0700

#### TAIWAN

Telephone: (86) 2 2657 6108

#### THAILAND

Telephone: (66) 2 515 2400

#### VIETNAM

Telephone: (65) 6477 7261

### International Offices

#### EUROPE

Website: [www.bradyeurope.com](http://www.bradyeurope.com)

#### NORTH AMERICA

Website: [www.bradynid.com](http://www.bradynid.com)