

Product  
Supplement



January 2010



# Table of Contents

Nissé.....	2
Noir.....	4
Equinox.....	10
Bay Court.....	12
Crestwood.....	14
Piedmont.....	16
Clayton.....	18
Willow Creek.....	22
Nicollette.....	28
Markor.....	32
Chloe.....	36
Brisas.....	38
Braiden.....	44
Nocera.....	48
Kensington.....	50
Janos.....	52
Westin.....	54
North Park.....	58
Lakeshore.....	64
Torino.....	66
Trinity, Modera, Essex.....	70
Brushed Nickel/Antique Bronze.....	72
Close-to-Ceiling.....	74
Ceiling Fans.....	80
Bath Collections.....	86
Le Papier Wall Sconces.....	110
Outdoor Collections.....	114
LED Recessed.....	124
Accessories.....	128
Index.....	129

*Left: P3902-20 two-light lantern with Thomasville® furniture from the Coterie™ collection and Thomasville Flooring® in Oak, Artisan finish.*



# Nissé



A glamorous, vintage modern pendant. Oval in shape, the pendant features a Polished Nickel finish with chunky discs of clear glass, cylinder bobeches and an optional center beaded column with a modern cut-prism drop. A rich off-white silken fabric shade completes the look.

P4431-104  
shown with center  
beaded column with  
cut prism drop



**OVAL CHANDELIER**  
**P4431-104** Polished Nickel  
Six-light with pendant.  
Size: 35-3/4" L., 17-5/8" W.,  
18-1/2" ht. Overall ht. w/chain  
94"; wire 15'.  
Lamps: Six candelabra base  
lamps, each 60w max.

*optional  
cut-prism  
drop*



*Cut prism drop*

P4431-104  
shown without  
cut prism drop



*Polished Nickel*

*Left: P4431-104 oval chandelier and P2772-101 Roxbury wall sconces with Thomasville® furniture from the Studio 455 collection.*



# Noir



*P4209-104 six-light chandelier and P2729-104 wall brackets, all with P8719-01 optional shades, with Thomasville® furniture from the Fredericksburg™ collection and Thomasville Flooring® in Makata hardwood.*





*Thomasville*  
LIGHTING®



# Noir

Extension of the Hollywood glamour style

This family coordinates with the Midnight Waltz and Roxbury collections, as well as individual pieces that display Regency styles and Art Deco undertones.

Shiny Polished Nickel finish

Faceted clear crystal center column and bobèche

Double tiered clear crystal drops with teardrop element, creating a cascading waterfall effect.

Accent these fixtures with optional black chiffon shades to intensify the dramatic effect.

P4209-104  
shown with optional  
shades P8719-01

*Polished Nickel*

*optional  
black chiffon fabric  
shades*



*classy crystal*

**THREE-LIGHT SEMI-FLUSH**  
**P3400-104** Polished Nickel  
Size: 13-1/2" dia., 14-1/2" ht.  
Lamps: Three candelabra base lamps, each 60w max.

P3400-104



P3400-104  
shown with optional  
shade P8772-01

**SIX-LIGHT CHANDELIER**  
**P4209-104** Polished Nickel  
Size: 28-1/2" dia., 33" ht. Overall  
ht. w/chain 108"; wire 15'.  
Lamps: Six candelabra base lamps, each 60w max.

P4209-104



Clear crystal drop





# Noir

P4208-104  
shown with optional  
shades P8719-01



P4208-104



P4208-104  
shown with optional  
shade P8772-01



Sheer black chiffon shade

**THREE-LIGHT CHANDELIER**  
**P4208-104** Polished Nickel  
Size: 16-1/2" dia., 23-1/4" ht.  
Overall ht. w/chain 98"; wire 15'.  
Lamps: Three candelabra base  
lamps, each 60w max.

clear  
crystal  
cascades



**OPTIONAL SHADE**  
**P8719-01** Sheer black chiffon  
Size: 4-1/2" dia., 5" ht.  
7/8" candle fitter.



Optional shades in high contrast  
black chiffon fabric in a sheer wrap  
are ideal for use in elegant dining  
rooms, formal sitting rooms and  
dramatic entryways.

**OPTIONAL SHADE**  
**P8772-01** Sheer black chiffon  
Size: 18" dia., 8-1/2" ht.

P4210-104

**NINE-LIGHT CHANDELIER**

**P4210-104** Polished Nickel

Two-tier.

Size: 32-1/2" dia., 35-1/2" ht.

Overall ht. w/chain 158"; wire 15'.

Lamps: Nine candelabra base lamps, each 60w max.



*without shades*

*with shades*



P2729-104  
shown with optional  
shades P8719-01



**WALL BRACKET**

**P2729-104** Polished Nickel

Two-light.

Size: 11-3/8" W., 16-3/4" ht.

Extends 5". H/CTR 7-7/8".

Lamps: Two candelabra base lamps, each 60w max.

P2729-104



# Equinox

Inspired by ancient astronomical armillary spheres

Interlocking rings pivot for an infinite variety of positions

Antique Bronze or Burnished Silver finish

Ideal for individual use over desktops and high-end workspaces – or can be used as multiple pieces over dining room tables and kitchen islands

See page 15 for optional wall mount accessory arm



P3827-126



P3827-20

**FOUR-LIGHT FOYER**  
**P3827-20** Antique Bronze  
**P3827-126** Burnished Silver  
Size: 16" dia., 18-3/8" ht. Overall  
ht. w/chain 94"; wire 15'.  
Lamps: Four candelabra base  
lamps, each 60w max.

*interlocking rings  
pivot for infinite positioning*

*Right: P3827-126 indoor lantern with  
Thomasville® furniture from the Casual  
Retreat™ collection.*



*Thomasville*  
LIGHTING®



# Bay Court





A contemporary interpretation of antique nautical lanterns

Updated cylinders in Brushed Nickel or Antique Bronze finish

This series of interior hanging lanterns can be used traditionally as foyer pieces, as well as in a non-traditional fashion – as single pieces or in multiples of two or more in dining rooms and kitchens.

See page 15 for optional wall mount accessory arm

*Brushed Nickel*



P3701-09

P3701-20

*Antique Bronze*



**ONE-LIGHT FOYER**

**P3701-09** Brushed Nickel

**P3701-20** Antique Bronze

Size: 11-3/4" dia., 18-1/4" ht. Overall ht. w/chain 94"; wire 15'.

Lamp: One medium base lamp, 100w max.

*distressed clear glass*

*& etched opal glass*

*Left: P3701-09 indoor lanterns with Thomasville Cabinetry® in Linden Maple Dover and Thomasville Flooring® in Jatoba hardwood.*

# Crestwood

Indoor lanterns are ideal for use in foyers and entryways, over dining tables and kitchen islands for an American Casual Urban lifestyle.

The essence of traditional gas lanterns with updated styling.

Clear glass panels are framed in metal finished in Antique Bronze or Burnished Silver finishes.



*classic style*

P3904-20

*in a variety of sizes*



**FOUR-LIGHT FOYER**  
P3904-20 Antique Bronze  
P3904-126 Burnished Silver  
Size: 18" sq., 26-3/4" ht.  
Overall ht. w/chain 102"; wire 15'.  
Lamps: Four candelabra base lamps, each 60w max.

P3902-126



P3902-20



**TWO-LIGHT FOYER**  
P3902-20 Antique Bronze  
P3902-126 Burnished Silver  
Size: 10-7/8" sq., 17-1/8" ht.  
Overall ht. w/chain 92"; wire 15'.  
Lamps: Two candelabra base lamps, each 60w max.

P3903-20



**THREE-LIGHT FOYER**  
P3903-20 Antique Bronze  
P3903-126 Burnished Silver  
Size: 14" sq., 21-1/8" ht.  
Overall ht. w/chain 96"; wire 15'.  
Lamps: Three candelabra base lamps, each 60w max.

**WALL MOUNT ACCESSORY ARM**

*Use the arm to convert the small and medium sized lanterns to wall bracket styles. The wire can be threaded through the open arm end to be direct-wired to a wall box. Hang the loop through the adjustable chain link to suspend the lantern. Maximum fixture wt. 20 lbs. Cannot be used with P3904 or P3888.*



*P3902-20 shown with optional accessory arm P8762-20*

**ACCESSORY ARM**  
P8762-09 Brushed Nickel  
P8762-20 Antique Bronze  
P8762-126 Burnished Silver  
Size: 4-3/4" W., 14-1/4" ht.  
Extends 11-3/4". H/CTR 9-3/4".



*Left: P3902-126 two-light lantern with Thomasville® furniture from the Coterie™ collection and Thomasville Flooring® in Oak, Artisan finish.*



*soaring arches*



P3884-20

**FOUR-LIGHT FOYER**  
**P3884-20** Antique Bronze  
**P3884-126** Burnished Silver  
Size: 13-3/8" sq., 20-3/8" ht.  
Overall ht. w/chain 95"; wire 15'.  
Lamps: Four candelabra base  
lamps, each 60w max.

Simple vertical structure with open arching roof and center lamp clusters inspired by classic Shaker design.

Antique Bronze or Burnished Silver finish

The open caged design is excellent for use in hallways, entryways, family rooms and dining tables and is suitable for a variety of styles, from American Urban to more eclectic tastes.

See page 15 for optional wall mount accessory arm

**EIGHT-LIGHT FOYER**  
**P3888-20** Antique Bronze  
**P3888-126** Burnished Silver  
Size: 17-1/4" sq., 34" ht.  
Overall ht. w/chain 109"; wire 15'.  
Lamps: Eight candelabra base  
lamps, each 60w max.  
Cannot be used with wall  
accessory arm.

*candle  
chaser  
accents*



P3888-126

**Thomasville**  
L I G H T I N G ®

Right: P3884-20 four-light foyer fixtures (with P8762-20 accessory arm) and P3888-20 eight-light foyer with Thomasville® furniture from the Wanderlust™ collection.



# Piedmont







*Thomasville*  
LIGHTING



# Clayton

Where classic vintage styling meets minimalistic lines. A traditionally rooted design with graceful arching arms, Clayton is highlighted by modern drum shades in cream linen fabric with soft side pleats.

Adjustable turnkey – for customized shade directions

Adjustable swing arm wall lamps can be either direct-wire mounted or portable mounted to the wall. Can function as a bedside or tableside reading lamp in place of a traditional table or floor lamp for today's less cluttered interiors.



P4421-84

*classic styling*

*linen drum shades*

## FOUR-LIGHT CHANDELIER

**P4421-84** Espresso

Size: 28-3/8" dia., 21-3/8" ht.

Overall ht. w/chain 96"; wire 15'.

Lamps: Four medium base lamps, each 100w max.

*Left: P2849-84 wall sconces and P5256-84 mini-pendants with furniture from the Wanderlust™ collection and the Highlife sofa and chair from Thomasville®.*



# Clayton

## LINEAR CHANDELIER

**P4400-84 Espresso**  
 Two-light. Includes two 6", one 12" and two 15" stems with 90° swivel.  
 Size: 40-3/4" L., 13-1/47" W., 31" ht.  
 Overall ht. w/stem 88"; wire 10'.  
 Lamps: Two medium base lamps, each 100w max.



P4400-84

*Espresso finish*

*direct wire or*



P2849-84

## WALL BRACKET

**P2849-84 Espresso**  
 One-light, portable wall mount with lamp cord. Can be installed as a direct wire or as a plug in. Arm swivels 90°. Low-high switch.  
 Size: 13-1/4" W., 22-3/8" ht. Extends 22-1/8". H/CTR 18-3/8".  
 Lamp: One medium base lamp, 100w max.



P2849-84  
 shown with wall cord (included)

*portable*



P5256-84

## MINI-PENDANT

**P5256-84 Espresso**  
 One-light, stem mount. Includes two 6", one 12" and two 15" stems with 90° swivel.  
 Size: 8-1/8" dia., 9" ht. Overall ht. w/stem 66"; wire 10'.  
 Lamp: One medium base lamp, 100w max.




**THREE-LIGHT PENDANT**  
**P3909-84** Espresso  
Bottom glass diffuser. Includes two 6", one 12" and two 15" stems with 90° swivel.  
Size: 20" dia., 21-7/8" ht.  
Overall ht. w/stem 79"; wire 10'.  
Lamp: Three medium base lamps, each 100w max.



P3759-84

**TWO-LIGHT SEMI-FLUSH**  
**P3759-84** Espresso  
Bottom glass diffuser.  
Size: 13" dia., 12-1/8" ht.  
Lamps: Two medium base lamps, each 100w max.



*Soft pleated linen drum shades and adjustable turn key arm backs.*



P4422-84

**FIVE-LIGHT CHANDELIER**  
**P4422-84** Espresso  
Size: 32" dia., 26-1/8" ht. Overall ht. w/chain 101"; wire 15'.  
Lamps: Five medium base lamps, each 100w max.



# Willow Creek

Weathered Auburn finish with subtle textured forged leaves

Organic forms fuse with modern lines to create an updated Global Craftsman feel

Hand-forged iron work

Unique pleated glass drum shades are incased glass with topaz finish



*Right: P4132-114 six-light chandelier, P2799-114 wall bracket and P2800-114 wall bracket with furniture from the Cinnamon Hill™ collection and the Celestial bench from Thomasville®.*



*Thomasville*  
L I G H T I N G .



# Willow Creek



P3463-114

**TWO-LIGHT SEMI-FLUSH**  
**P3463-114** Weathered Auburn  
Chain and ceiling mounts both included.  
Size: 16" dia., 16-1/2" ht. Overall ht. w/chain 92"; wire 15'.  
Lamps: Two medium base lamps, each 100w max.



P3463-114

**LINEAR CHANDELIER**  
**P4130-114** Weathered Auburn  
Two-light.  
Size: 44" L., 13" W., 34" ht.  
Overall ht. w/chain 109"; wire 15'.  
Lamps: Two medium base lamps, each 150w max.

P4130-114



*spiraling scrolls*



P5101-114



P5101-114



P5101-114

*natural inspirations*

**MINI-PENDANT**

**P5101-114** Weathered Auburn  
Includes two 6", one 12" and two 15" stems with 90° swivel.  
Size: 11-3/4" dia., 20-3/4" ht.  
Overall ht. w/stem 75"; wire 10'.  
Lamp: One medium base lamp, 150w max.




P5133-114

**ONE-LIGHT PENDANT**

**P5133-114** Weathered Auburn  
Includes two 6", one 12" and two 15" stems with 90° swivel.  
Size: 14-3/8" dia., 22" ht.  
Overall ht. w/stem 79"; wire 10'.  
Lamp: One medium base lamp, 150w max.

*soft pleated glass*



*Textured forged ironwork*



# Willow Creek

P4132-114

**SIX-LIGHT CHANDELIER**  
**P4132-114** Weathered Auburn  
Size: 30" dia., 28-3/8" ht. Overall  
ht. w/chain 103"; wire 15'.  
Lamps: Six medium base lamps,  
each 100w max.

*Weathered Auburn*



*left*

*and*

*right*

P2799-114

**WALL BRACKET – LEFT**  
**P2799-114** Weathered Auburn  
Two-light.  
Size: 16-5/8" W., 17-1/2" ht.,  
Extends 9". H/CTR 10".  
Lamps: Two medium base  
lamps, each 100w max.  
Damp location listed.



P2800-114

**WALL BRACKET – RIGHT**  
**P2800-114** Weathered Auburn  
Two-light.  
Size: 16-5/8" W., 17-1/2" ht.,  
Extends 9". H/CTR 10".  
Lamps: Two medium base  
lamps, each 100w max.  
Damp location listed.



P4131-114

**THREE-LIGHT CHANDELIER**  
**P4131-114** Weathered Auburn  
Size: 19" dia., 22" ht. Overall ht.  
w/chain 97"; wire 15'.  
Lamps: Three medium base  
lamps, each 100w max.



*Pleated glass shade*

*forged leaves*



P3908-114

**FOUR-LIGHT FOYER**  
**P3908-114** Weathered Auburn  
Size: 19-5/8" dia., 32-1/2" ht.  
Overall ht. w/chain 107-1/2";  
wire 15'.  
Lamps: Four medium base  
lamps, each 100w max.



# Nicollette

Whimsical take on delicate ribbon scrollwork with a nod to the French Riviera lifestyle, for an updated style.

The tapered drum glass shades feature a classic damask scroll pattern etched into the glass.

Available in either Copper Bronze or Brushed Nickel finish.



P4453-124

*Copper Bronze*



**FIVE-LIGHT CHANDELIER**

**P4453-09** Brushed Nickel

**P4453-124** Copper Bronze

Size: 25-1/2" dia., 19-1/8" ht.

Overall ht. w/chain 103"; wire 15'.

Lamps: Five medium base lamps, each 100w max.



*Ribbon scrollwork*

P4448-09

*Brushed Nickel*



P4448-124



**THREE-LIGHT CHANDELIER**

**P4448-09** Brushed Nickel

**P4448-124** Copper Bronze

Size: 21-1/4" dia., 24-1/2" ht.

Overall ht. w/chain 100"; wire 15'.

Lamps: Three medium base lamps, each 100w max.



# Nicollette

*versatile mini-pendant combo*



*Glass etched with classic damask scroll pattern*



P5191-124



P5191-124



P5191-09



P5191-09

**MINI-PENDANT COMBO**  
**P5191-09** Brushed Nickel  
**P5191-124** Copper Bronze  
 One-light. Mini-pendant can convert to close-to-ceiling when mounted without chain.  
 Size: 6-3/8" dia., 14-3/4" ht.  
 Overall ht. w/chain 90"; wire 15'.  
 Lamp: One medium base lamp, 100w max.



P2723-124



P2723-09

**WALL BRACKET**  
**P2723-09** Brushed Nickel  
**P2723-124** Copper Bronze  
 One-light.  
 Size: 6-3/8" W., 11" ht.  
 Extends 9".  
 Lamp: One medium base lamp, 100w max.  
 Damp location listed.

P3862-09



*Brushed Nickel*

P3862-124



*Copper Bronze*

**TWO LIGHT SEMI-FLUSH**

**P3862-09** Brushed Nickel

**P3862-124** Copper Bronze

Size: 12-3/8" dia., 9-1/4" ht.

Lamps: Two medium base lamps, each 100w max.

Damp location listed.

P3917-09



P3917-124



**THREE-LIGHT PENDANT**

**P3917-09** Brushed Nickel

**P3917-124** Copper Bronze

Size: 19-1/4" dia., 18-3/8" ht.

Overall ht. w/chain 95"; wire 15'.

Lamps: Three medium base lamps, each 100w max.

# Markor

With a vintage modern flair, Markor is inspired by mid-century design.

Markor's modular pendant approach offers the ability to create a unique look by selecting from choices of fabrics, shade sizes and pendant kits.

All shades include a bottom etch acrylic diffuser to provide even luminance.

See page 34 for ordering instructions.





# Modular Pendants

Shade and pendant kit are sold separately. 16" and 22" shades can be used with pendant kit P5198 or P5199. See page 34-35 for ordering information.

*Modular design*



*Color & size choices*

*Left: P8824-01 22" drum shade and P5199-09 pendant kit.*

# Markor Modular Pendant

Shade and pendant kit are sold separately.

10" shades can be used only with pendant kit P5198.



Beige silken fabric and diffuser

P8765-01  
shown with  
P5198-09 pendant kit



10" DRUM SHADE  
**P8765-01** Chloe Floral Fabric  
Acrylic bottom diffuser.  
For use with P5198 only.  
Size: 10" dia., 8" ht.

P8821-01  
shown with  
P5198-09 pendant kit



10" DRUM SHADE  
**P8821-01** Beige Silken Fabric  
Acrylic bottom diffuser.  
For use with P5198 only.  
Size: 10" dia., 8" ht.

P8820-01  
shown with  
P5198-20 pendant kit



10" DRUM SHADE  
**P8820-01** Black Parchment  
Paper with White Liner  
Acrylic bottom diffuser.  
For use with P5198 only.  
Size: 10" dia., 8" ht.

## Pendant Kits



P5198-20

**ONE-LIGHT PENDANT KIT**  
**P5198-09** Brushed Nickel  
**P5198-20** Antique Bronze  
One-light pendant kit for use with  
Markor or Chloe shades. Includes  
two 6", one 12" and two 15" stems  
with 90° swivel.  
Size: 1-5/8" dia., 5-5/8" ht. Overall  
ht. w/stem and lamp 66"; wire 10'.  
Lamp: One medium base lamp,  
100w max.



P5199-09


**THREE-LIGHT PENDANT KIT**  
**P5199-09** Brushed Nickel  
**P5199-20** Antique Bronze  
Three-light pendant kit for use with  
Markor or Chloe 16" and 22" shades.  
Includes two 6", one 12" and two 15"  
stems with 90° swivel.  
Size: 4-3/4" dia., 6-1/4" ht. Overall  
ht. w/stem and lamps 64"; wire 10'.  
Lamps: Three medium base lamps,  
each 100w max.

# Modular Pendant System

## Simple to order

Specify three separate pieces – fabric, shade size, and stem kit of your choice – to order the Markor or Chloe modular pendant

### Step 1: Choose a fabric



Chloe linen white-on-white floral pattern



Markor black parchment paper with white liner



Markor beige silken fabric

### Step 2: Select a shade size and stem kit

#### 10" SMALL SHADE

- P8765-01** Chloe Floral Fabric
- P8820-01** Markor Black Parchment Paper
- P8821-01** Markor Beige Silken Fabric

*10" small shades can only be used with P5198 one-light pendant kit*



#### P5198 ONE-LIGHT PENDANT KIT

- P5198-09** Brushed Nickel
- P5198-20** Antique Bronze



#### 16" MEDIUM SHADE

- P8766-01** Chloe Floral Fabric
- P8822-01** Markor Black Parchment Paper
- P8823-01** Markor Beige Silken Fabric

*16" medium shades can be used with P5198 one-light pendant kit or P5199 three-light pendant kit*



#### P5199 THREE-LIGHT PENDANT KIT

- P5199-09** Brushed Nickel
- P5199-20** Antique Bronze



#### P5198 ONE-LIGHT PENDANT KIT

- P5198-09** Brushed Nickel
- P5198-20** Antique Bronze



#### 22" LARGE SHADE

- P8768-01** Chloe Floral Fabric
- P8824-01** Markor Black Parchment Paper
- P8825-01** Markor Beige Silken Fabric

*22" large shades can be used with P5198 one-light pendant kit or P5199 three-light pendant kit*



#### P5199 THREE-LIGHT PENDANT KIT

- P5199-09** Brushed Nickel
- P5199-20** Antique Bronze



#### P5198 ONE-LIGHT PENDANT KIT

- P5198-09** Brushed Nickel
- P5198-20** Antique Bronze





# Chloe Modular Pendant

Shade and pendant kit are sold separately. 16" and 22" shades can be used with pendant kit P5198 or P5199. See page 34-35 for ordering information.

*Chloe pendants are ...*

**P8765-01**  
shown with  
P5198-09 pendant kit



*versatile*

**10" SHADE**  
**P8765-01** Chloe Floral Fabric  
For use with P5198 only.  
Size: 10" dia., 8" ht.

**P8766-01**  
shown with  
P5199-20 pendant kit



*modular*

**16" SHADE**  
**P8766-01** Chloe Floral Fabric  
For use with P5198 or P5199.  
Size: 16" dia., 10" ht.

*white-on-white  
patterned fabric*

**P8768-01**  
shown with  
P5199-09 pendant kit



*stylish*

**22" DRUM SHADE**  
**P8768-01** Chloe Floral Fabric  
For use with P5198 or P5199.  
Size: 22" dia., 10" ht.

# Chloe

Simple, straight forward design with a twist.

Elegant Copper Bronze metallic finish complements the elongated suspended metal tubes.

Unique oval shaped cased opal glass with white- on-white abstract floral pattern that conveys a simple, lighter lifestyle.

P5028-124

## MINI-PENDANT

**P5028-124** Copper Bronze  
Includes two 6", one 12" and two 15" stems with 90° swivel.  
Size: 5-1/4" dia., 9-1/4" ht.  
Overall ht. w/stem 66"; wire 10'.  
Lamp: One medium base lamp, 100w max.




P4051-124



## SIX-LIGHT CHANDELIER

**P4051-124** Copper Bronze  
Size: 24-1/4" dia., 25" ht.  
Overall ht. w/chain 100"; wire 15'.  
Lamps: Six medium base lamps, each 100w max.

See page 98 for the Chloe bath collection



Unique oval shades can be mounted in either configuration

# Brisas

Brisas – a soft tropical breeze – features elegant bamboo-inspired elements

Leaf clusters and banded metal arms delicately complement the scrollwork, which is joined together by bands depicting rattan wrapping

A Burnished Ebony finish is complemented by soft golden highlights and antique mist shades with etched bamboo pattern glass.

P3795-127

*Burnished Ebony*

*bamboo inspired accents*

THREE-LIGHT  
INVERTED PENDANT  
**P3795-127** Burnished Ebony  
Size: 26" dia., 38-1/4" ht. Overall  
ht. w/chain 114"; wire 15'.  
Lamps: Three medium base  
lamps, each 100w max.







P3720-127

**FOUR-LIGHT FOYER**  
**P3720-127** Burnished Ebony  
 Size: 21" dia., 46-3/4" ht. Overall  
 ht. w/chain 122"; wire 15'.  
 Lamps: Four medium base lamps,  
 each 100w max.



P5155-127



P5155-127

*elegant  
 etching*

**MINI-PENDANT**  
**P5155-127** Burnished Ebony  
 Size: 9-3/4" dia., 18" ht.  
 Overall ht. w/chain 93"; wire 15'.  
 Lamp: One medium base lamp,  
 100w max.



P7100-127

**WALL SCONCE**  
**P7100-127** Burnished Ebony  
 One-light.  
 Size: 18-1/2" W., 13" ht.  
 Extends 7". H/CTR 4-1/2".  
 Lamp: One medium base  
 lamp, 100w max.

Billy  
  
 Moon

# Brisas



## THREE-LIGHT SEMI-FLUSH

**P3905-127** Burnished Ebony  
Chain and ceiling mounts both included.

Size: 17" dia., 21-1/2" ht. Overall ht. w/chain 96"; wire 15'.

Lamps: Three medium base lamps, each 100w max.



Leaf detail

*Burnished Ebony*

P4383-127



## THREE-LIGHT CHANDELIER

**P4383-127** Burnished Ebony

Size: 23" dia., 30-1/2" ht.

Overall ht. w/chain 106"; wire 15'.

Lamps: Three medium base lamps, each 100w max.

P4429-127

*leaf accents*

**NINE-LIGHT CHANDELIER**

**P4429-127** Burnished Ebony

Two-tier.

Size: 35" dia., 45-1/2" ht.

Overall ht. w/chain 169"; wire 15'.

Lamps: Nine medium  
base lamps, each 100w max.



*rattan inspirations*





P4384-127

P2761-127

**LINEAR CHANDELIER**  
**P4384-127** Burnished Ebony  
Three-light.  
Size: 41-3/4" L., 9-3/4" W.,  
34-3/4" ht. Overall ht. w/  
chain 110"; wire 15'.  
Lamps: Three medium base  
lamps, each 100w max.


**WALL BRACKET**  
**P2761-127** Burnished Ebony  
One-light.  
Size: 15-1/4" W., 13" ht.  
Extends 6-1/2".  
Lamp: One medium base  
lamp, 100w max.  
Damp location listed.

*etched bamboo pattern*

# Braiden

Silhouetted chandeliers framed by delicate woven wire elements and braided metal details. The woven wire cups can be removed for a customized design.

Globally-influenced woven wire accents ideal for showcasing other global and hand woven home décor accessories in areas such as living rooms, dining rooms and bedrooms.



*Woven wire detail*



P4484-84

## THREE-LIGHT CHANDELIER

**P4484-84** Espresso

Size: 20-1/4" dia., 23-3/4" ht.

Overall ht. w/chain 99"; wire 15'.

Lamps: Three medium base lamps, each 100w max.

*with wire cups*

P4484-84  
shown without  
wire cups



*or without*



P5175-84

## MINI-PENDANT

**P5175-84** Espresso

Includes two 6", one 12" and two 15" stems with 90° swivel.

Size: 6" dia., 14-1/2" ht.

Overall ht. w/stem 72"; wire 10'.

Lamp: One medium base lamp, 100w max.

P4487-84



*misted wheat  
glass*

*artisan wirework*

SIX-LIGHT CHANDELIER  
P4487-84 Espresso  
Size: 30" dia., 34-1/2" ht. Overall  
ht. w/chain 158"; wire 15'.  
Lamps: Six medium base lamps,  
each 100w max.



# Braiden

## TWO-LIGHT SEMI-FLUSH

**P3739-84** Espresso

Chain and ceiling mounts both included.

Size: 15" dia., 16" ht. Overall ht. w/chain 91"; wire 15'.

Lamps: Two medium base lamps, each 75w max.



P3739-84



P3739-84



*Misted wheat glass and woven wire basket*



P7072-84

## WALL SCONCE

**P7072-84** Espresso

One-light.

Size: 13-1/4" W., 7" ht. Extends 6-3/4".

Lamp: One medium base lamp, 100w max.



P4485-84

## FIVE-LIGHT CHANDELIER

**P4485-84** Espresso

Size: 23-1/2" dia., 26" ht. Overall ht. w/chain 101"; wire 15'.

Lamps: Five medium base lamps, each 100w max.

P3890-84

*earthy Espresso*



**THREE-LIGHT INVERTED  
PENDANT**

**P3890-84 Espresso**

Size: 24" dia., 28-1/4" ht. Overall  
ht. w/chain 103"; wire 15'.

Lamps: Three medium base  
lamps, each 100w max.

*wispy  
woven  
wire*

# Nocera

Forged metal with fluid intersecting arms and unique twisted center columns, all finished in Oil Rubbed Bronze, capturing a casual lodge lifestyle.

The glass bowls have an inside pebble texture with smooth outside finish in a light topaz haze.

**THREE-LIGHT CHANDELIER**  
**P4424-108** Oil Rubbed Bronze  
Size: 19-3/4" dia., 19-3/8" ht.  
Overall ht. w/chain 94"; wire 15'.  
Lamps: Three medium base lamps, each 100w max.



*Oil Rubbed Bronze*

*intersecting arms*



**THREE-LIGHT FOYER**  
**P3869-108** Oil Rubbed Bronze  
Size: 19-3/4" dia., 25-1/2" ht.  
Overall ht. w/chain 99"; wire 15'.  
Lamps: Three medium base lamps, each 100w max.




**MINI-PENDANT**  
**P5075-108** Oil Rubbed Bronze  
Includes two 6", one 12" and two 15" stems with 90° swivel.  
Size: 5-3-4" dia., 17-1/2" ht.  
Overall ht. w/stem 75"; wire 10'.  
Lamp: One medium base lamp, 100w max.





*light topaz  
haze glass*

**TWO-LIGHT SEMI-FLUSH**  
**P3291-108** Oil Rubbed Bronze  
 Chain and ceiling mounts both included.  
 Size: 16-1/2" dia., 14" ht.  
 Overall ht. w/chain 91"; wire 15'.  
 Lamps: Two medium base lamps, each 100w max.



*Glass with smooth outer surface and pebble textured interior*



**WALL BRACKET**  
**P3183-108** Oil Rubbed Bronze  
 One-light.  
 Size: 5-3/4" W., 9-7/8" ht.  
 Extends 8".  
 Lamp: One medium base lamp, 100w max.  
 Damp location listed

**FIVE-LIGHT CHANDELIER**  
**P4426-108** Oil Rubbed Bronze  
 Size: 24" dia., 22" ht. Overall ht. w/chain 97"; wire 15'.  
 Lamps: Five medium base lamps, each 100w max.

See page 97 for the Nocera bath collection



# Kensington

This traditionally-rooted collection features scrolled metalwork in a Forged Bronze finish.

Trumpet-shaped, slightly textured glass shades are complemented by a frosted caramel swirl finish.



P2783-77

*Mount up*



P2783-77

*or down*

## WALL BRACKET

**P2783-77** Forged Bronze

One-light.

Size: 6" W., 9-1/2" ht.

Extends 7".

Lamp: One medium base lamp, 100w max.

Damp location listed.

## FOUR-LIGHT FOYER

**P3464-77** Forged Bronze

Size: 18" dia., 29" ht. Overall ht.

w/chain 104"; wire 15'.

Lamps: Four medium base

lamps, each 100w max.



P3464-77

*Forged Bronze*



P4158-77

## THREE-LIGHT CHANDELIER

**P4158-77** Forged Bronze

Size: 18" dia., 20-1/2" ht.

Overall ht. w/chain 96"; wire 15'.

Lamps: Three medium base

lamps, each 100w max.



P5141-77



P5141-77

## MINI-PENDANT

**P5141-77** Forged Bronze

Includes two 6", one 12" and

two 15" stems with 90° swivel.

Size: 7" dia., 7-1/2" ht.

Overall ht. w/stem 65"; wire 10'.

Lamp: One medium base lamp, 100w max.



P3532-77

**THREE-LIGHT FOYER**  
**P3532-77** Forged Bronze  
Size: 21-7/8" dia., 28-1/4" ht.  
Overall ht. w/chain 103";  
wire 15'.  
Lamps: Three medium base  
lamps, each 100w max.


*trumpet  
shaped  
shades*



P3829-77

*frosted carmel  
swirl glass*

**TWO-LIGHT SEMI-FLUSH**  
**P3829-77** Forged Bronze  
Size: 14" dia., 12" ht.  
Lamps: Two medium base  
lamps, each 100w max.  
Damp location listed.



*Frosted carmel swirl glass*



P4238-77

**FIVE-LIGHT CHANDELIER**  
**P4238-77** Forged Bronze  
Size: 27" dia., 26-1/2" ht.  
Overall ht. w/chain 96"; wire 15'.  
Lamps: Five medium base lamps,  
each 100w max.

See page 104 for the Kensington bath collection





# Janos

Simplistic curved arms are held by a center ring, delivering a minimalist urban style. Offered in Brushed Nickel with modern trumpet glass shades in a soft etched finish.

**FIVE-LIGHT CHANDELIER**  
**P4483-09** Brushed Nickel  
Size: 25-5/8" dia., 19-3/4" ht.  
Overall ht. w/chain 95"; wire 15'.  
Lamps: Five medium base lamps, each 100w max.



P4483-09

**THREE-LIGHT CHANDELIER**  
**P4481-09** Brushed Nickel  
Size: 20-5/8" dia., 16-1/2" ht.  
Overall ht. w/chain 92"; wire 15'.  
Lamps: Three medium base lamps, each 100w max.



P4481-09

P4488-09

*Brushed Nickel*

**NINE-LIGHT CHANDELIER**  
**P4488-09** Brushed Nickel  
Two-tier.  
Size: 28" dia., 29" ht. Overall ht. w/chain 104"; wire 15'.  
Lamps: Nine medium base lamps, each 100w max.



*minimalist urban design*

P4482-09

**FOUR-LIGHT CHANDELIER**

**P4482-09** Brushed Nickel  
Size: 21-3/4" dia., 19-1/8" ht.  
Overall ht. w/chain 94"; wire 15'.  
Lamps: Four medium base lamps,  
each 100w max.



P3855-09

**TWO-LIGHT SEMI-FLUSH**

**P3855-09** Brushed Nickel  
Size: 13-3/8" dia., 8-3/8" ht.  
Lamps: Two medium base lamps,  
each 100w max.  
Damp location listed.



*soft etched glass*

P3919-09

**THREE-LIGHT FOYER**

**P3919-09** Brushed Nickel  
Size: 16-3/8" dia., 22" ht. Overall  
ht. w/chain 97"; wire 15'.  
Lamps: Three medium base  
lamps, each 100w max.



P5282-09

**ONE-LIGHT PENDANT**

**P5282-09** Brushed Nickel  
Includes two 6", one 12" and  
two 15" stems with 90° swivel.  
Size: 16-1/8" dia., 8-1/2" ht.  
Overall ht. w/stem 65"; wire 15'.  
Lamp: One medium base lamp,  
100w max.



P5176-09

**MINI-PENDANT**

**P5176-09** Brushed Nickel  
Includes two 6", one 12" and  
two 15" stems with 90° swivel.  
Size: 6" dia., 7-1/2" ht.  
Overall ht. w/stem 64"; wire 10'.  
Lamp: One medium base lamp,  
100w max.



See page 105 for the Janos bath collection









# Westin

Additions to the popular Westin collection are now available, offering even more options for this simple, modern and elegant family.

The Westin family features a sculptured, linear look with a touch of metal, perfect for today's understated interiors.

*Left: P7127-09 two-light wall sconce, P3509-09 three-light foyer, and P4439-09 chandelier.*

# Westin

## CEILING FAN LIGHT KIT

**P2649-09** Brushed Nickel

**P2649-20** Antique Bronze

Etched glass.

Size: 11" dia., 7" ht.

Lamps: Three candelabra base lamps, each 40w max. 190 watt EPACT limiter.




P2649-09

*etched glass*



P2649-20



*Forged ironwork*



P7127-09

## WALL SCONCE

**P7127-09** Brushed Nickel

**P7127-20** Antique Bronze

Two-light.

Size: 12-3/4" W., 13-5/8" ht.

Extends 5-7/8". H/CTR9-3/4".

Lamps: Two candelabra base lamps, each 60w max.



P7127-20

*Antique Bronze*

P5167-20

P5167-09



*Brushed Nickel*

## MINI-PENDANT

**P5167-09** Brushed Nickel

**P5167-20** Antique Bronze

Includes two 6", one 12" and two 15" stems with 90° swivel.

Size: 3-3/4" dia., 9-3/4" ht.

Overall ht. w/stem 67"; wire 10'.

Lamp: One medium base lamp, 100w max.

Socket tool included (pg. 128).

# Westin CFL



The new Westin CFL family recently received the 2008 Lighting for Tomorrow award in the indoor fixture CFL family category for its innovative use of state-of-the-art and energy efficient technology creating decorative – yet functional – fixtures.

Incorporating a minimalist design style, this award-winning collection represents a shift in trends to highlight a less complicated, clean design.

**THREE-LIGHT CFL FOYER**  
**P3757-09EBWB** Brushed Nickel  
**P3757-20EBWB** Antique Bronze  
 Size: 18-1/8" dia., 25" ht.  
 Overall ht. w/chain 100"; wire 15'.  
 Lamps: Three 13w CFL, included.  
 GU24 base.



P3757-09EBWB

P3509-20EBWB



P3509-09EBWB



**THREE-LIGHT CFL FOYER**  
**P3509-09EBWB** Brushed Nickel  
**P3509-20EBWB** Antique Bronze  
 Size: 12" dia., 26" ht. Overall ht.  
 w/chain 101"; wire 15'.  
 Lamps: Three 13w CFL, included.  
 GU24 base.



P5108-09EBWB



P5108-20EBWB



**CFL MINI-PENDANT**  
**P5108-09EBWB** Brushed Nickel  
**P5108-20EBWB** Antique Bronze  
 Includes two 6", one 12" and two 15" stems with 90° swivel.  
 Size: 4" dia., 6-3/4" ht. Overall ht.  
 w/stem 120"; wire 15'.  
 Lamp: One 13w CFL, included.  
 GU24 base.





# Westin CFL

Arching, elegant arms with strap accents compliment the etched glass in the Westin line.

Fixtures are available in Brushed Nickel and Antique Bronze finishes and use the latest dedicated GU-24 lamp technology.

P2649-09EBWB



P2649-20EBWB



## CFL CEILING FAN LIGHT KIT

**P2649-09EBWB** Brushed Nickel

**P2649-20EBWB** Antique Bronze

Etched glass.

Size: 11" dia., 7" ht.

Lamps: Two 13w CFL (included).

GU24 base. 190 watt EPACT limiter.



P4436-20EBWB



P4436-09EBWB



## FIVE-LIGHT CFL CHANDELIER

**P4436-09EBWB** Brushed Nickel

**P4436-20EBWB** Antique Bronze

Size: 22" dia., 26-3/8" ht. Overall ht. w/chain 101"; wire 15'.

Lamps: Five 13w CFL, included.

GU24 base.



*arching strap arms*

P3290-09EBWB



P3290-20EBWB



*efficient CFLs*

CFL CLOSE-TO-CEILING  
**P3290-09EBWB** Brushed Nickel  
**P3290-20EBWB** Antique Bronze  
Two light.  
Size: 14" dia., 7" ht.  
Lamps: Two 13w CFL, included.  
GU24 base.  
Damp location listed.



P4435-09EBWB



*elegant style*



*Textured forged ironwork*

P4435-20EBWB



CFL LINEAR CHANDELIER  
**P4435-09EBWB** Brushed Nickel  
**P4435-20EBWB** Antique Bronze  
Four-light. Stem Mounted  
Size: 35" L., 12-1/2" W., 29" ht.  
Overall ht. w/stem 79"; wire 15".  
Lamps: Four 13w CFL, included.  
GU24 base.



See page 106 for the Westin CFL bath collection



# North Park

Clean linear forms, twin structural arching arms and square etched glass shades create a modern interpretation of two blended styles: Craftsman and Mission.

Available in either Brushed Nickel finish, for a modern approach or Venetian Bronze finish, for a classic look, this collection was developed to reflect the growing trend in Craftsman style architecture and newer hardware styles.

*linear forms*



P4003-09



P4003-74

## LINEAR CHANDELIER

**P4003-09** Brushed Nickel

**P4003-74** Venetian Bronze

Six-light.

Size: 27-1/4" L., 14-1/4" W., 22-5/8"

ht. Overall ht. w/chain 98"; wire 15'.

Lamps: Six medium base lamps,  
each 100w max.

P4004-09



## EIGHT-LIGHT CHANDELIER

**P4004-09** Brushed Nickel

**P4004-74** Venetian Bronze

Size: 27-1/4" dia., 24-5/8" ht.

Overall ht. w/chain 100"; wire 15'.

Lamps: Eight medium base lamps,  
each 100w max.

**MINI-PENDANT**

**P5135-09** Brushed Nickel  
**P5135-74** Venetian Bronze  
Includes two 6", one 12" and two 15" stems with 90° swivel.  
Size: 5-1/2" dia., 7-1/8" ht.  
Overall ht. w/stem 64-1/8";  
wire 15'.  
Lamp: One medium base lamp, 100w max.



P5135-09



P5135-74

P3907-74

**EIGHT-LIGHT FOYER**  
**P3907-09** Brushed Nickel  
**P3907-74** Venetian Bronze  
Two-tier.  
Size: 18" dia., 32" ht. Overall ht. w/chain 155"; wire 15'.  
Lamps: Eight medium base lamps, each 100w max.



P4053-74

*square etched shades*

**TWELVE-LIGHT CHANDELIER**

**P4053-09** Brushed Nickel  
**P4053-74** Venetian Bronze  
Two-tier.  
Size: 27-1/4" dia., 30-1/8" ht.  
Overall ht. w/chain 154"; wire 15'.  
Lamps: Twelve medium base lamps, each 100w max.



# North Park



P4001-09



P4001-74

**FOUR-LIGHT CHANDELIER**  
**P4001-09** Brushed Nickel  
**P4001-74** Venetian Bronze  
Size: 21" dia., 19-5/8" ht. Overall  
ht. w/chain 95"; wire 15'.  
Lamps: Four medium base  
lamps, each 100w max.



P4002-74

**FOUR-LIGHT CHANDELIER**  
**P4002-09** Brushed Nickel  
**P4002-74** Venetian Bronze  
Size: 21" dia., 22-3/4" ht. Overall  
ht. w/chain 98"; wire 15'.  
Lamps: Four medium base  
lamps, each 100w max.

*Venetian Bronze*



P4002-09


*Brushed Nickel*

CLOSE-TO-CEILING

**P3852-09** Brushed Nickel  
**P3852-74** Venetian Bronze  
Two-light.  
Size: 15" sq., 7-1/8" ht.  
Lamps: Two medium base lamps, each 100w max.  
Damp location listed.



P3852-74



P3854-09

CLOSE-TO-CEILING

**P3854-09** Brushed Nickel  
**P3854-74** Venetian Bronze  
One-light.  
Size: 12-1/2" sq., 6-1/8" ht.  
Lamp: One medium base lamp, 100w max.  
Damp location listed.



P3906-09



P3597-74

P3597-09

TWO-LIGHT SEMI-FLUSH

**P3597-09** Brushed Nickel  
**P3597-74** Venetian Bronze  
Chain and ceiling mounts both included.  
Size: 12-3/4" sq., 13-5/8" ht.  
Overall ht. w/chain 89"; wire 15'.  
Lamps: Two medium base lamps, each 100w max.



P3906-74

TWO-LIGHT INVERTED PENDANT

**P3906-09** Brushed Nickel  
**P3906-74** Venetian Bronze  
Size: 16" sq., 24-1/8" ht. Overall ht. w/chain 100"; wire 15'.  
Lamps: Two medium base lamps, each 100w max.

*Craftsman style*

See page 102 for the North Park bath collection



# Lakeshore

Simplified soft modern style with nature-inspired undertones. Smooth on the outside, Lakeshore's glass projects an impression of looking at pebbles through water.

The gentle curved arms compliment the diagonal struts, keeping the design uncluttered and clean for today's interiors.



P2710-09

## WALL BRACKET

**P2710-09** Brushed Nickel  
One-light.  
Size: 5" W., 9-7/8" ht.  
Extends 7".  
Lamp: One medium base lamp, 100w max.  
Damp location listed



P5168-09



P5168-09

## MINI-PENDANT

**P5168-09** Brushed Nickel  
Includes two 6", one 12" and two 15" stems with 90° swivel.  
Size: 5" dia., 8-1/4" ht.  
Overall ht. w/stem 65"; wire 10".  
Lamp: One medium base lamp, 100w max.



P4466-09

## THREE-LIGHT CHANDELIER

**P4466-09** Brushed Nickel  
Size: 19" dia., 19" ht.  
Overall ht. w/chain 94"; wire 15'.  
Lamps: Three medium base lamps, each 100 max.



P3918-09

## THREE-LIGHT FOYER

**P3918-09** Brushed Nickel  
Size: 23-3/8" dia., 25" ht.  
Overall ht. w/chain 100"; wire 15'.  
Lamps: Three medium base lamps, each 100w max.

*Brushed Nickel*

P3861-09



**TWO LIGHT SEMI-FLUSH**  
**P3861-09** Brushed Nickel  
Size: 14" dia., 10-1/2" ht.  
Lamps: Two medium base lamps, each 100w max.

P3920-09



**THREE-LIGHT FOYER**  
**P3920-09** Brushed Nickel  
Size: 16" dia., 27" ht.  
Overall ht. w/chain 102"; wire 15'.  
Lamps: Three candelabra base lamps, each 60w max.


P4468-09



*gentle curves*

*modern style*

**FIVE-LIGHT CHANDELIER**  
**P4468-09** Brushed Nickel  
Size: 24-3/4" dia., 24" ht.  
Overall ht. w/chain 99"; wire 15'.  
Lamps: Five medium base lamps, each 100w max.



Pebble glass

See page 100 for the Lakeshore bath collection





# Torino

New Brushed Nickel finish in this American Casual collection now bridges on Soft Modern with etched glass.

P5144-09

*squared scrolls*

P5144-09



## ONE-LIGHT FOYER

**P5144-09** Brushed Nickel  
Stem and ceiling mounts both included. Includes one 6", one 12" and two 15" stems with swivel.  
Size: 13-1/8" dia., 15-1/8" ht.  
Overall ht. w/stem 66"; wire 10'.  
Lamp: One medium base lamp, 100w max.

P4417-09



## SIX-LIGHT CHANDELIER

**P4417-09** Brushed Nickel  
Size: 28-5/8" dia., 29-7/8" ht.  
Overall ht. w/chain 105"; wire 15'.  
Lamps: Six medium base lamps, each 100w max. and three medium base lamps, each 75w max.

P4416-09



## FIVE-LIGHT CHANDELIER

**P4416-09** Brushed Nickel  
Size: 26-1/8" dia., 24-3/4" ht. Overall ht. w/chain 100"; wire 15'.  
Lamps: Five medium base lamps, each 100w max.



P3184-09

**CLOSE-TO-CEILING**

**P3184-09** Brushed Nickel

Two light.

Size: 14-5/8" dia., 7-1/8" ht.

Lamps: Two medium base lamps, each 100w max.

Damp location listed.



P2645-09

**CEILING FAN LIGHT KIT**

**P2645-09** Brushed Nickel

Universal style with quick-connect wiring. Etched glass.

Size: 12" dia., 5-3/4" ht.

Lamps: Two candelabra base lamps (included), each 60w max.

190 watt EPACT limiter.



P4419-09

*Brushed Nickel*

**TWELVE-LIGHT CHANDELIER**

**P4419-09** Brushed Nickel

Three-tier.

Size: 34" dia., 41-5/8" ht. Overall ht. w/chain 164"; wire 15'.

Lamps: Twelve medium base lamps, each 100w max.



P7181-09

**WALL SCONCE**

**P7181-09** Brushed Nickel

One-light.

Size: 9-1/2" W., 6-3/4" ht.

Extends 4-3/4". H/CTR 2-7/8".

Lamp: One medium base lamp, 100w max.

# Torino

## THREE-LIGHT FOYER

**P3843-09** Brushed Nickel  
Chain and ceiling mounts both included.

Size: 18" dia., 18-1/2" ht.  
Overall ht. w/chain 94"; wire 15'.  
Lamps: Three medium base lamps, each 100w max.



P3843-09



P3843-09

*etched glass*



P4405-09

## THREE-LIGHT CHANDELIER

**P4405-09** Brushed Nickel  
Size: 19-1/8" dia., 19-1/8" ht.  
Overall ht. w/chain 94"; wire 15'.  
Lamps: Three medium base lamps, each 100w max.



P3847-09

*sleek curves*

## THREE-LIGHT FOYER

**P3847-09** Brushed Nickel  
Size: 22" dia., 27" ht. Overall ht. w/chain 102"; wire 15'.  
Lamps: Three medium base lamps, each 100w max.

See page 101 for the Torino bath collection





P4415-09

**THREE-LIGHT CHANDELIER**

**P4415-09** Brushed Nickel

Size: 24" dia., 24-1/8" ht. Overall ht. w/chain 99"; wire 15'.

Lamps: Three medium base lamps, each 100w max. and one medium base lamp, 75w max.



P3824-09

**THREE-LIGHT FOYER**

**P3824-09** Brushed Nickel

Size: 19-3/4" dia., 32-1/2" ht. Overall ht. w/chain 108"; wire 15'.

Lamps: Three medium base lamps, each 100w max.



P4418-09

**NINE-LIGHT CHANDELIER**

**P4418-09** Brushed Nickel

Two-tier.

Size: 32" dia., 32-5/8" ht. Overall ht. w/chain 155"; wire 15'.

Lamps: Nine medium base lamps, each 100w max. and three medium base lamps, each 75w max.



P5153-09

**MINI-PENDANT**

**P5153-09** Brushed Nickel

Includes one 6", one 12" and two 15" stems with swivel.

Size: 7-1/2" dia., 11" ht. Overall ht. w/stem 68"; wire 10'.

Lamp: One medium base lamp, 100w max.



# Trinity

Brushed Nickel, Polished Brass, Antique Bronze or Cobblestone finish

Etched glass

See Progress Lighting Catalog 128 for more of our popular Trinity collection

## FIFTEEN-LIGHT CHANDELIER

**P4365-09** Brushed Nickel

**P4365-10** Polished Brass

**P4365-20** Antique Bronze

**P4365-33** Cobblestone

Three-tier.

Size: 43-3/4" dia., 43-5/8" ht.

Overall ht. w/chain 167"; wire 15'.

Lamps: Fifteen medium base lamps, each 75w max.



## Modera Mini-pendant

Glass-in-glass mid-century inspired mini-pendant.

A clean outside glass orb captures the inside etched opal diffuser.

Finish is Polished Nickel.

## MINI-PENDANT

**P5174-104** Polished Nickel

One-light. Includes one 6", one 12" and two 15" stems with swivel.

Size: 11-3/8" dia., 10-1/8" ht.

Overall ht. w/stem 67"; wire 10'.

Lamp: One medium base lamp, 100w max.





## Essex Foyer

Clear hurricane glass shade

Antique Nickel finish

THREE-LIGHT FOYER  
**P3617-81** Antique Nickel  
Size: 11-3/4" dia., 22" ht.  
Overall ht. w/chain 97";  
wire 15'.  
Lamps: Three candelabra  
base lamps, each 60w max.



# Brushed Nickel and Antique Bronze

Alabaster glass shades

P3457-20



P3457-09



## CLOSE-TO-CEILING

**P3457-09** Brushed Nickel

**P3457-20** Antique Bronze

Two-light.

Size: 13-3/8" dia., 6-3/4" ht.

Lamps: Two medium base lamps,  
each 60w max.

Damp location listed.

P3458-20



P3458-09



*soft scrolls*

P3459-09



## FOUR-LIGHT FOYER

**P3458-09** Brushed Nickel

**P3458-20** Antique Bronze

Size: 15-7/8" dia., 25-7/8"

ht. Overall ht. w/chain

101"; wire 15'.

Lamps: Four candelabra  
base lamps, each 60w max.

## THREE-LIGHT FOYER

**P3459-09** Brushed Nickel

**P3459-20** Antique Bronze

Size: 18-7/8" dia., 28-1/2"

ht. Overall ht. w/chain

104"; wire 15'.

Lamps: Three medium base  
lamps, each 60w max.

*See page 107 for the Brushed Nickel/  
Antique Bronze bath collection*



P3460-20



P3460-09



**TWO-LIGHT SEMI-FLUSH**  
**P3460-09** Brushed Nickel  
**P3460-20** Antique Bronze  
Size: 13-1/4" dia., 13-3/4" ht.  
Lamps: Two medium base lamps, each 60w max..

P7153-09



P7153-20

**WALL SCONCE**  
**P7153-09** Brushed Nickel  
**P7153-20** Antique Bronze  
One-light.  
Size: 15-3/8" W., 7" ht.  
Extends 7-1/2". H/CTR 2-1/2".  
Lamp: One medium base lamp, 60w max.

*classic curves*

P3459-20



P5091-09



P5091-20



**ONE-LIGHT PENDANT**  
**P5091-08** Brushed Nickel  
**P5091-20** Antique Bronze  
Size: 15-3/8" dia., 16-1/2" ht.  
Overall ht. w/chain 56"; wire 10'.  
Lamp: One medium base lamp, 100w max.



# Close-to-ceiling

## Clayton

**P3759-84 Espresso**  
Two-light semi-flush.  
Size: 13" dia., 12-1/8" ht.  
Lamps: Two medium base lamps, each 100w max.

**Thomasville**  
LIGHTING®



## Braiden

**P3739-84 Espresso**  
Two-light semi-flush.  
Size: 15" dia., 16" ht.  
Lamps: Two medium base lamps, each 75w max.



## Willow Creek

**P3463-114 Weathered Auburn**  
Two-light semi-flush.  
Size: 16" dia., 16-1/2" ht. .  
Lamps: Two medium base lamps, each 100w max.

**Thomasville**  
LIGHTING®



## Kensington

**P3829-77 Forged Bronze**  
Two-light semi-flush.  
Size: 14" dia., 12" ht.  
Lamps: Two medium base lamps, each 100w max.  
Damp location listed.

*See page 104 for the Kensington bath collection*



## Brisas

**P3905-127 Burnished Ebony**  
Three-light semi-flush.  
Size: 17" dia., 21-1/2" ht.  
Lamps: Three medium base lamps, each 100w max.

*See page 96 for the Brisas bath collection*



**Billy**  
**Moon**

## Nocera

**P3291-108** Oil Rubbed Bronze  
Two-light semi-flush.  
Size: 16-1/2" dia., 14" ht.  
Lamps: Two medium base lamps, each 100w max.



P3291-108

See page 97 for the Nocera bath collection



## Lakeshore

**P3861-09** Brushed Nickel  
Two-light semi-flush.  
Size: 14" dia., 10-1/2" ht.  
Lamps: Two medium base lamps, each 100w max.  
Damp location listed.



P3861-09

See page 100 for the Lakeshore bath collection



## Janos

**P3855-09** Brushed Nickel  
Two-light.  
Size: 13-3/8" dia., 8-3/8" ht.  
Lamps: Two medium base lamps, each 100w max.  
Damp location listed.



P3855-09

See page 105 for the Janos bath collection



## Torino

**P3184-09** Brushed Nickel  
Two-light.  
Size: 14-5/8" dia., 7-1/8" ht.  
Lamps: Two medium base lamps, each 100w max.  
Damp location listed.



P3184-09

See page 101 for the Torino bath collection



## Nicollette

**P3862-09** Brushed Nickel  
**P3862-124** Copper Bronze  
Two-light semi-flush.  
Size: 12-3/8" dia., 9-1/4" ht.  
Lamps: Two medium base lamps, each 100w max.  
Damp location listed.



P3862-09



P3862-124

# Close-to-ceiling

## North Park

**P3597-09** Brushed Nickel  
**P3597-74** Venetian Bronze  
Two-light semi-flush  
Size: 12-3/4" dia., 13-5/8" ht.  
Overall ht. w/chain 89"; wire 15'.  
Lamps: Two medium base lamps, each 100w max.



## North Park

**P3852-09** Brushed Nickel  
**P3852-74** Venetian Bronze  
Two-light.  
Size: 15" sq., 7-1/8" ht.  
Lamps: Two medium base lamps, each 100w max.  
Damp location listed.



## North Park

**P3854-09** Brushed Nickel  
**P3854-74** Venetian Bronze  
One-light.  
Size: 12-1/2" dia., 6-1/8" ht.  
Lamp: One medium base lamp, 100w max.  
Damp location listed



## Lynzie

**P3863-15** Polished Chrome  
Two-light.  
Size: 13" dia., 7-1/4" ht.  
Lamps: Two medium base lamps, each 75w max.  
Damp location listed.



See page 102 for the North Park bath collection



See page 99 for the Lynzie bath collection



# Lahara

**P3836-03** Aged Pewter

**P3836-09** Brushed Nickel

**P3836-15** Polished Chrome

**P3836-74** Venetian Bronze

Two-light.

Size: 13" dia., 6-1/8" ht.

Lamps: Two medium base lamps, each 100w max.

Damp location listed.



See page 90 for the Lahara bath collection



P3836-09



P3836-15



P3836-03



P3836-74



# Addison

**P3870-03** Aged Pewter

**P3870-09** Brushed Nickel

**P3870-15** Polished Chrome

**P3870-74** Venetian Bronze

Two-light.

Size: 12-5/8" dia., 6-1/8" ht.

Lamps: Two medium base lamps, each 100w max.

Damp location listed.



See page 86 for the Addison bath collection



P3870-09



P3870-74



P3870-15





# Close-to-ceiling

## Westin CFL

**P3290-09EBWB** Brushed Nickel

**P3290-20EBWB** Antique Bronze

Two light.

Size: 14" dia., 7" ht.

Lamps: Two 13w CFL, included.

GU24 base.

Damp location listed.



See page 106 for the Westin CFL bath collection



P3290-09EBWB



P3290-20EBWB



## Melon Glass CFL

**P3816-09EBWB** Brushed Nickel

**P3816-20EBWB** Antique Bronze

**P3816-30EBWB** White

One-light

Size: 11-3/8" dia., 6" ht.

Lamp: One 13w CFL, included.

GU24 base.

Damp location listed.



**P3817-09EBWB** Brushed Nickel

**P3817-20EBWB** Antique Bronze

**P3817-30EBWB** White

Two-light.

Size: 13-1/4" dia., 7" ht.

Lamps: Two 13w CFL, included

GU24 base.

Damp location listed.



P3816-30EBWB



P3816-20EBWB



P3817-09EBWB



P3817-20EBWB



## Maier CFL



**P3910-09** Brushed Nickel

One-light. Etched white opal glass.

Size: 9" dia., 4" ht.

Lamp: One 26w CFL.

GU24 base.

Damp location listed.



P3910-09



P3911-09



**P3911-09** Brushed Nickel

Two-light. Etched white opal glass.

Size: 14" dia., 4-1/2" ht.

Lamps: Two 26w CFL.

GU24 base.

Damp location listed.



# New Bedford

Brushed Nickel or Antique Bronze finish

Etched seeded glass

See Progress Lighting Catalog 128 for more of our popular New Bedford collection

**P3866-09** Brushed Nickel  
**P3866-20** Antique Bronze  
 One-light.  
 Size: 11" dia., 5-1/2" ht.  
 Lamp: One medium base lamp, 100w max.  
 Damp location listed.



P3866-20

**P3867-09** Brushed Nickel  
**P3867-20** Antique Bronze  
 One-light.  
 Size: 13" dia., 5-3/4" ht.  
 Lamps: Two medium base lamps, each 75w max.  
 Damp location listed.



P3867-09

**P3462-09** Brushed Nickel  
**P3462-20** Antique Bronze  
 One-light foyer.  
 Size: 8" dia., 11" ht.  
 Lamp: One medium base lamp, 100w max.



P3462-09



P3462-20

# Brushed Nickel and Antique Bronze

**P3457-09** Brushed Nickel  
**P3457-20** Antique Bronze  
 Two-light.  
 Size: 13-3/8" dia., 6-3/4" ht.  
 Lamps: Two medium base lamps, each 60w max.  
 Damp location listed.



P3457-09



P3457-20

**P3460-09** Brushed Nickel  
**P3460-20** Antique Bronze  
 Two-light semi-flush.  
 Size: 13-1/4" dia., 13-3/4" ht.  
 Lamps: Two medium base lamps, each 60w max..



P3460-20

See page 107 for the Brushed Nickel/  
 Antique Bronze bath collection



# Ceiling Fans

## 60" Signature Fan

**P2532-09** Brushed Nickel with reversible Natural Cherry/Cherry blades

**P2532-20** Antique Bronze with reversible Medium Cherry/Classic Walnut blades

**P2532-80** Forged Black with reversible Dark Cherry/Dark Walnut blades

Remote control included. Three speed fan operation and full range dimming for light. Uplight and downlight wired separately for independent or simultaneous control (Requires two circuits). Size: 60" dia., 16-5/8" ht.

Lamps: Four candelabra base uplight lamps (included), each 7w.



30-year limited warranty

SureConnect® blade arms

12° blade pitch

45° canopy (up to 12:12 ceiling pitch)

Triple capacitor 188mm x 20mm reversible motor

80" lead wires

Plywood blade construction

Light fixture adaptable

CUL

### ENERGY INFORMATION AT HIGH SPEED

Airflow: 5,947 cubic feet per minute

Electricity Use: 68 watts (excludes lights)

Airflow Efficiency: 87 cubic feet per minute per watt

Compare: 49" to 60" ceiling fans have airflow efficiencies ranging from approximately 51 to 176 cubic feet per minute per watt at high speed.



P2532-20  
Medium Cherry blades



Classic Walnut blades



P2532-80  
Dark Cherry blades



Dark Walnut blades



P2532-09  
Natural Cherry blades



Cherry blades

# 54" Signature Plus Fan

**P2530-09** Brushed Nickel with reversible Silver/Natural Cherry blades

**P2530-20** Antique Bronze with reversible Medium Cherry/Classic Walnut blades

**P2530-30W** White with White blades  
Size: 54" dia., 15" ht.

30-year limited warranty  
12° blade pitch  
45° canopy (up to 12:12 ceiling pitch)  
Triple capacitor 153mm x 18mm  
reversible motor  
80" lead wires  
MDF blade construction  
Light fixture adaptable  
CUL



P2530-09  
Silver blades



Natural Cherry blades

## ENERGY INFORMATION AT HIGH SPEED

Airflow: 5,362 cubic feet per minute

Electricity Use: 65 watts (excludes lights)

Airflow Efficiency: 82 cubic feet per minute per watt

Compare: 49" to 60" ceiling fans have airflow efficiencies ranging from approximately 51 to 176 cubic feet per minute per watt at high speed.



P2530-20  
Classic Walnut blades



Medium Cherry blades



P2530-30W  
White blades



# Ceiling Fans

## 52" Patio Fan

**P2502-80** Forged Black with Toasted Oak blades  
Indoor/outdoor fan with stainless steel hardware.  
Five blades.  
Size: 52" dia., 17-3/8" ht. 12-3/16" CTC ht.

15-year limited warranty  
SureConnect® blade arms  
12° blade pitch  
Dual mount  
Quick-Install canopy  
Triple capacitor, 153mm x 17.5mm reversible motor  
72" lead wires  
ABS all-weather blades  
Light fixture adaptable  
CUL listed for wet locations

### ENERGY INFORMATION AT HIGH SPEED

Airflow: 5,061 cubic feet per minute

Electricity Use: 56 watts (excludes lights)

Airflow Efficiency: 90 cubic feet per minute per watt

Compare: 49" to 60" ceiling fans have airflow efficiencies ranging from approximately 51 to 176 cubic feet per minute per watt at high speed.

See Progress Catalog 128 for information on White (-30), Cobblestone (-33), and Antique Bronze (-20) finishes.



P2502-80  
Toasted Oak blades

## 54" Patio Fan

**P2533-20** Antique Bronze with Toasted Oak blades  
Size: 54" dia., 18-3/4" ht.

15-year limited warranty  
SureConnect® blade arms  
12° blade pitch  
45° canopy (up to 12:12 ceiling pitch)  
Triple capacitor 153mm x 18mm reversible motor  
80" lead wires  
ABS all-weather blades  
Light fixture adaptable  
CUL listed for wet locations

### ENERGY INFORMATION AT HIGH SPEED

Airflow: 5,647 cubic feet per minute

Electricity Use: 58 watts (excludes lights)

Airflow Efficiency: 97 cubic feet per minute per watt

Compare: 49" to 60" ceiling fans have airflow efficiencies ranging from approximately 51 to 176 cubic feet per minute per watt at high speed.



P2533-20  
Toasted Oak blades

# 30" Builder Fan

**P2529-09** Brushed Nickel with reversible White/Natural Cherry blades  
**P2529-20** Antique Bronze with reversible Classic Walnut/Medium Cherry blades  
**P2529-30W** White with White blades  
 Size: 30" dia., 13-1/4" ht. 9-7/16" CTC ht.  
 15-year limited warranty  
 18° blade pitch  
 Quick-Install canopy (up to 4:12 ceiling pitch)  
 Triple capacitor 153mm x 10mm reversible motor  
 80" lead wires  
 MDF blade construction  
 Light fixture adaptable  
 CUL

**ENERGY INFORMATION AT HIGH SPEED**  
 Airflow: 2,398 cubic feet per minute  
 Electricity Use: 46 watts (excludes lights)  
 Airflow Efficiency: 52 cubic feet per minute per watt  
 Compare: 36" to 48" ceiling fans have airflow efficiencies ranging from approximately 71 to 86 cubic feet per minute per watt at high speed.



P2529-09  
 White blades  
  
 Natural Cherry blades




P2529-20  
 Medium Cherry blades  
  
 Classic Walnut blades


# 42" Builder Fan

**P2500-09** Brushed Nickel with reversible Cherry/Natural Cherry blades  
**P2500-20** Antique Bronze with reversible Classic Walnut/Medium Cherry blades  
 Size: 42" dia., 12-1/4" ht. 8-1/2" CTC ht.  
 15-year limited warranty  
 SureConnect® blade arms  
 11° blade pitch  
 Quick-Install canopy (up to 4:12 ceiling pitch)  
 Triple capacitor 153mm x 10mm reversible motor  
 72" lead wires  
 MDF blade construction  
 Light fixture adaptable  
 CUL



P2500-09  
 Cherry blades  
  
 Natural Cherry blades



P2500-20  
 Classic Walnut blades  
  
 Medium Cherry blades

**ENERGY INFORMATION AT HIGH SPEED**  
 Airflow: 2,415 cubic feet per minute  
 Electricity Use: 49 watts (excludes lights)  
 Airflow Efficiency: 50 cubic feet per minute per watt  
 Compare: 36" to 48" ceiling fans have airflow efficiencies ranging from approximately 71 to 86 cubic feet per minute per watt at high speed.

# Ceiling Fan Light Kits

## Westin

**P2649-09** Brushed Nickel  
**P2649-20** Antique Bronze  
 Etched glass.  
 Size: 11" dia., 6" ht.  
 Lamps: Three candelabra base lamps, each 40w max, included.  
 190 watt EPACK limiter.

P2649-20  
 P2649-20EBWB



P2649-09  
 P2649-09EBWB



## Westin CFL

**P2649-09EBWB** Brushed Nickel  
**P2649-20EBWB** Antique Bronze  
 Indoor. Etched glass. Universal-style with quick-connect wiring.  
 Size: 11" dia., 6" ht.  
 Lamps: Two 13w CFL, included (non-dimmable). GU-24 base.  
 190-watt EPACK limiter.

## Pavilion

**P2653-09** Brushed Nickel  
**P2653-20** Antique Bronze  
 Indoor. Etched watermark glass. Universal-style with quick-connect wiring.  
 Size: 12" dia., 5-11/16" ht.  
 Lamps: Three candelabra base lamps, 40w max., included.  
 190-watt EPACK limiter.

P2653-09



P2653-20



*Also coordinates with Sentura and Richmond Hill collections. See Progress Catalog 128 for more information.*

## Torino

**P2645-09** Brushed Nickel with etched glass  
**P2645-77** Forged Bronze with tea-stained glass  
 Universal-style with quick-connect wiring.  
 Size: 12" dia., 5-11/16" ht.  
 Lamps: Three candelabra base lamps, 40w max., included.  
 190-watt EPACK limiter.

P2645-09



P2645-77



## Low Profile

**P2602-09EBWB** Brushed Nickel  
**P2602-20EBWB** Antique Bronze  
**P2602-30EBWB** White  
 Indoor. Opal glass. Universal style with quick-connect wiring.  
 Size: 10-5/8" dia., 3-7/8" ht.  
 Lamps: Two 13w CFL, included (non-dimmable). GU24 base.  
 190-watt EPACK limiter.

P2602-09EBWB



P2602-30EBWB



P2602-20EBWB



## New Bedford

**P2648-09** Brushed Nickel  
**P2648-20** Antique Bronze  
 Universal style with quick-connect wiring. Etched seeded glass.  
 Size: 16-1/2" dia., 7-1/8" ht.  
 Lamps: Three candelabra base lamps (included), each 60w max.  
 190 watt EPACK limiter.

P2648-09



P2648-20



## Schoolhouse

**P2601-80** Forged Black  
 Indoor/outdoor. Opal glass.  
 Universal style with quick-connect wiring.  
 Size: 8-1/2" dia., 6-3/4" ht.  
 Lamp: One medium base lamp, 60w max. One 13w medium base CFL included (non-dimmable).

P2601-80



## Fan/Light Remote



**P2618-01** Fan/Light Remote  
 Provides fan speed and light control from convenient handheld remote. Compatible with non-dimmable compact fluorescent lamps. For single pole applications. Receiver fits in fan canopy.

See Progress Catalog 128 for information on White (-30), Cobblestone (-33), and Antique Bronze (-20) finishes.





# Addison

Inspired by the sophisticated scalloped cuts in a seashell, Addison features graceful, curved arms and delicate scalloped glass shades with an etched glass finish. The collection was developed to coordinate with the 2009 Delta Faucet collection.

Mounts up or down.

Damp location listed.

See pages 88-89 for additional finishes.

P3870-74



**P3870-74** Venetian Bronze  
Two-light close-to-ceiling.  
Size: 12-5/8" dia., 6" ht.  
Lamps: Two medium base  
lamps, each 100w max.

## Venetian Bronze



P2847-74



P2846-74



P2848-74

Product No.	Finish	Description	Size	Lamp(s)
P2846-74	Venetian Bronze	One-light	5-1/2" W., 9-3/8" ht. Extends 6-3/8".	1 medium base, 100w max.
P2847-74	Venetian Bronze	Two-light	15-7/8" W., 9" ht. Extends 6-3/8".	2 medium base, each 100w max.
P2848-74	Venetian Bronze	Three-light	26" W., 9" ht. Extends 6-3/8".	3 medium base, each 100w max.

*coordinates with Delta  
Faucet fixtures*

Left: P2846-74 one-light bath and P2847-74 two-light bath fixtures and Delta's Addison faucets.



# Addison



*Aged Pewter*

P2848-03



P2847-03



*Brushed Nickel*

P2848-09



P2846-03

*mount up or down*



P2847-09



P2846-09

P3870-15



*Polished Chrome*

P3870-09



**P3870-03** Aged Pewter  
**P3870-09** Brushed Nickel  
**P3870-15** Polished Chrome  
**P3870-74** Venetian Bronze  
 Two-light close-to-ceiling.  
 Size: 12-5/8" dia., 6" ht.  
 Lamps: Two medium base  
 lamps, each 100w max.



P2848-15



P2847-15



P2846-15

P2846-15

Product No.	Finish	Description	Size	Lamp(s)
<b>P2846-03</b>	Aged Pewter	One-light	5-1/2" W., 9-3/8" ht.	1 medium base,
<b>P2846-09</b>	Brushed Nickel		Extends 6-3/8".	100w max.
<b>P2846-15</b>	Polished Chrome			
<b>P2846-74</b>	Venetian Bronze			
<b>P2847-03</b>	Aged Pewter	Two-light	15-7/8" W., 9" ht.	2 medium base,
<b>P2847-09</b>	Brushed Nickel		Extends 6-3/8".	each 100w max.
<b>P2847-15</b>	Polished Chrome			
<b>P2847-74</b>	Venetian Bronze			
<b>P2848-03</b>	Aged Pewter	Three-light	26" W., 9" ht.	3 medium base,
<b>P2848-09</b>	Brushed Nickel		Extends 6-3/8".	each 100w max.
<b>P2848-15</b>	Polished Chrome			
<b>P2848-74</b>	Venetian Bronze			

*coordinates with Delta  
 Faucet fixtures*







# Lahara

This timeless design works with a variety of bath decors, and coordinates with Delta's popular Lahara faucet design.

Mounts up or down.

Damp location listed.

See pages 92-93 for additional finishes.

P3836-09



**P3836-09** Brushed Nickel  
Two-light close-to-ceiling.  
Size: 13" dia., 6-1/8" ht.  
Lamps: Two medium base  
lamps, each 100w max.  
Damp location listed.



P2758-09

*mount up or down*



P2758-09



P2760-09



P2759-09

*Brushed Nickel*

Product No.	Finish	Description	Size	Lamp(s)
P2758-09	Brushed Nickel	One-light	5-3/4" W., 10-3/8" ht. Extends 7-1/2"	1 medium base, 100w max.
P2759-09	Brushed Nickel	Two-light	15-5/8" W., 10-3/8" ht. Extends 7-1/2"	2 medium base, each 100w max.
P2760-09	Brushed Nickel	Three-light	25-3/8" W., 10-3/8" ht. Extends 7-1/2"	3 medium base, each 100w max.

*Left: P2758-09 one-light bath and P2760-09 three-light bath fixtures and Delta's Lahara faucet.*

*coordinates with Delta  
Faucet fixtures*



# Lahara



P3836-03

*Aged Pewter*

**P3836-03** Aged Pewter  
**P3836-09** Brushed Nickel  
**P3836-15** Polished Chrome  
**P3836-74** Venetian Bronze  
 Two-light close-to-ceiling.  
 Size: 13" dia., 6-1/8" ht.  
 Lamps: Two medium base lamps, each 100w max.  
 Damp location listed.



P2758-03

*mount up or down*



P2759-03



P2760-03



P2758-74



P2758-74

Product No.	Finish	Description	Size	Lamp(s)
<b>P2758-03</b>	Aged Pewter	One-light	5-13/16" W., 10-7/16" ht.	1 medium base, 100w max.
<b>P2758-09</b>	Brushed Nickel			
<b>P2758-15</b>	Polished Chrome		Extends 7-1/2".	
<b>P2758-74</b>	Venetian Bronze			
<b>P2759-03</b>	Aged Pewter	Two-light	15-5/8" W., 10-3/8" ht.	2 medium base, each 100w max.
<b>P2759-09</b>	Brushed Nickel			
<b>P2759-15</b>	Polished Chrome		Extends 7-1/2".	
<b>P2759-74</b>	Venetian Bronze			
<b>P2760-03</b>	Aged Pewter	Three-light	25-3/8" W., 10-3/8" ht.	3 medium base, each 100w max.
<b>P2760-09</b>	Brushed Nickel			
<b>P2760-15</b>	Polished Chrome		Extends 7-1/2".	
<b>P2760-74</b>	Venetian Bronze			

P3836-74



P3836-15



*Venetian Bronze*



P2759-74

P2758-15



P2760-74



P2759-15

*Polished Chrome*



P2760-15

*coordinates with Delta*

*Faucet fixtures*







# Glenmont

Clean lines with geometric forms lends the collection to a variety of today's simplified lifestyles.

Aged Pewter or Venetian Bronze finish added to our popular Glenmont collection in Brushed Nickel and Polished Chrome.

Coordinates with Delta's Dryden Collection.

Mounts up or down.

Damp location listed.



P3135-74



P3135-03




P3136-74

*Venetian Bronze*



P3137-74



P3136-03

*Aged Pewter*



P3137-03

Product No.	Finish	Description	Size	Lamp(s)
P3135-03	Aged Pewter	One-light	5-3/4" W., 8-3/4" ht.	1 medium base,
P3135-74	Venetian Bronze		Extends 7-3/4".	100w max.
P3136-03	Aged Pewter	Two-light	14-3/4" W., 8-3/4" ht.	2 medium base,
P3136-74	Venetian Bronze		Extends 7-3/4".	each 100w max.
P3137-03	Aged Pewter	Three-light	21" W., 8-1/4" ht.	3 medium base,
P3137-74	Venetian Bronze		Extends 6-1/4".	each 100w max.

See Progress Catalog 128 for information on Polished Chrome (-15) or Brushed Nickel (-09) finishes

Left: P3135-03 one-light bath and P3137-03 three-light bath fixtures and Delta's Dryden faucets.

*coordinates with  
Delta Faucet fixtures*



# Brisas

Leaf clusters and banded metal arms delicately complement the scrollwork, which is joined together by bands depicting rattan wrapping

A Burnished Ebony finish is complemented by soft golden highlights and antique mist with etched bamboo pattern glass.

Mounts up or down.

Damp location listed.



P2762-127



P2761-127



P2763-127



P2764-127

Product No.	Finish	Description	Size	Lamp(s)
P2761-127	Burnished Ebony	One-light	15-1/4" W., 13" ht. Extends 6-1/2".	1 medium base, 100w max.
P2762-127	Burnished Ebony	Two-light	18" W., 13-1/2" ht. Extends 6-1/2".	2 medium base, each 100w max.
P2763-127	Burnished Ebony	Three-light	25" W., 12-3/4" ht. Extends 6-1/2".	3 medium base, each 100w max.
P2764-127	Burnished Ebony	Four-light	35" W., 13" ht. Extends 6-1/2".	4 medium base, each 100w max.

See pages 38-43 for more of the Brisas collection



# Nocera

**TWO-LIGHT SEMI-FLUSH**  
**P3291-108** Oil Rubbed Bronze  
 Chain and ceiling mounts both included.  
 Size: 16-1/2" dia., 14" ht.  
 Overall ht. w/chain 91"; wire 15'.  
 Lamps: Two medium base lamps, each 100w max.



P3291-108

Forged metal work with fluid intersecting arms, all finished in Oil Rubbed Bronze. The glass has an inside pebble texture with smooth outside finish in a light topaz haze.

Mounts up or down.

Damp location listed.

*pebbled topaz glass*



P3185-108



P3183-108



P3183-108

*Oil Rubbed Bronze*



P3194-108

Product No.	Finish	Description	Size	Lamp(s)
P3183-108	Oil Rubbed Bronze	One-light	5-3/4" W., 9-7/8" ht. Extends 8".	1 medium base, 100w max.
P3185-108	Oil Rubbed Bronze	Two-light	17-1/4" W., 9-7/8" ht. Extends 8".	2 medium base, each 100w max.
P3194-108	Oil Rubbed Bronze	Three-light	23-1/4" W., 9-7/8" ht. Extends 8".	3 medium base, each 100w max.

See pages 48-49 for more of the Nocera collection





# Chloe

Simple straightforward design with a twist.

Elegant Copper Bronze finish complements unique oval-shaped opal glass with white-on-white floral pattern.

Damp location listed.

*Copper Bronze*



P2715-124



P2755-124

*mount up...*



P2756-124

*... or down*

*white-on-white patterned shades*



P2716-124

Product No.	Finish	Description	Size	Lamp(s)
P2715-124	Copper Bronze	One-light	5-1/4" W., 10-3/8" ht. Extends 5-5/8".	1 medium base, 100w max.
P2716-124	Copper Bronze	Two-light	14-1/2" W., 11-1/8" ht. Extends 5-5/8".	2 medium base, each 100w max.
P2755-124	Copper Bronze	Three-light	24" W., 11-1/8" ht. Extends 5-5/8".	3 medium base, each 100w max.
P2756-124	Copper Bronze	Four-light	33-1/4" W., 11-1/8" ht. Extends 5-5/8".	4 medium base, each 100w max.

# Lynzie

A cousin to the Chloe collection, similarly uncluttered and simple lines depict the gracefulness of the Lynzie bath collection. Etched white oval shaped glass shades are held by delicate classic chrome finished arms.

Damp location listed.



P2802-15



P2801-15



P3863-15



P2803-15

*elegant style*

**P3863-15** Polished Chrome Two-light close-to-ceiling. Size: 13" dia., 7-1/4" ht. Lamps: Two medium base lamps, each 75w max. Damp location listed.

*oval shades*



P2804-15

*Polished Chrome*

Product No.	Finish	Description	Size	Lamp(s)
P2801-15	Polished Chrome	One-light	5-1/4" W., 10-3/8" ht. Extends 5-5/8".	1 medium base, 100w max.
P2802-15	Polished Chrome	Two-light	14-1/2" W., 11-1/8" ht. Extends 5-5/8".	2 medium base, each 100w max.
P2803-15	Polished Chrome	Three-light	24" W., 11-1/8" ht. Extends 5-5/8".	3 medium base, each 100w max.
P2804-15	Polished Chrome	Four-light	33-1/4" W., 11-1/8" ht. Extends 5-5/8".	4 medium base, each 100w max.

# Lakeshore

Lakeshore is simple and clean, for today's interiors.  
Perfect for spa-inspired bath suites.

Smooth on the outside, pebbled glass projects an image  
as if looking at pebbles through water.

Mounts up or down.

Damp location listed.



**P3861-09** Brushed Nickel  
Two light semi-flush.  
Size: 14" dia., 10-1/2" ht.  
Lamps: Two medium base  
lamps, each 100w max.  
Damp location listed.



P2710-09



*Brushed Nickel*

P2711-09

*clean styling for an  
uncluttered lifestyle*



P2712-09

*pebbled glass*

Product No.	Finish	Description	Size	Lamp(s)
<b>P2710-09</b>	Brushed Nickel	One-light	5" W., 9-7/8" ht. Extends 7".	1 medium base, 100w max.
<b>P2711-09</b>	Brushed Nickel	Two-light	14" W., 8-3/8" ht. Extends 7".	2 medium base, each 100w max.
<b>P2712-09</b>	Brushed Nickel	Three-light	23" W., 8-3/4" ht. Extends 7".	3 medium base, each 100w max.

*See pages 64-65 for more of the Lakeshore collection*



# Laguna

Ocean waves inspired the Laguna collection, resulting in a modern design infused with elements from nature.

Unique oval shades with an incised wave pattern in etched opal glass creates a sophisticated silhouette. A high polish Chrome finish highlights the design.

Mounts up or down.

Damp location listed.



P3089-15WB



P3089-15WB

*oval shaped  
incised wave pattern  
etched opal glass*



P3090-15WB



P3091-15WB

*Polished Chrome*

Product No.	Finish	Description	Size	Lamp(s)
<b>P3089-15WB</b>	Polished Chrome	One-light	7" W., 8-3/4" ht. Extends 5-1/4".	1 xenon, 60w max. (included)
<b>P3090-15WB</b>	Polished Chrome	Two-light	15-1/2" W., 7-7/8" ht. Extends 5-1/4".	2 xenon, each 60w max. (included)
<b>P3091-15WB</b>	Polished Chrome	Three-light	24" W., 7-7/8" ht. Extends 5-1/4".	3 xenon, each 60w max. (included)



**P7807-01** 60w Krypton xenon replacement lamp.



# North Park

Clean linear forms and square etched glass create a modern interpretation of two blended styles – Craftsman and Mission.

Mounts up or down.


Damp location listed.



**P3854-09** Brushed Nickel  
**P3854-74** Venetian Bronze  
 One-light close-to-ceiling.  
 Size: 12-1/2" sq., 6-1/8" ht.  
 Lamp: One medium base lamp,  
 100w max.




**P3852-09** Brushed Nickel  
**P3852-74** Venetian Bronze  
 Two-light close-to-ceiling.  
 Size: 15" sq., 7-1/8" ht.  
 Lamps: Two medium base lamps,  
 each 100w max.



P2745-09

*square etched glass*



P2738-74



P2743-74



P2733-09

Product No.	Finish	Description	Size	Lamp(s)
<b>P2733-09</b>	Brushed Nickel	One-light	5-1/2" W., 10-1/8" ht.	1 medium base,
<b>P2733-74</b>	Venetian Bronze		Extends 7-1/8".	100w max.
<b>P2738-09</b>	Brushed Nickel	Two-light	14-1/4" W., 9" ht.	2 medium base,
<b>P2738-74</b>	Venetian Bronze		Extends 7-1/8".	each 100w max.
<b>P2743-09</b>	Brushed Nickel	Three-light	23" W., 9" ht.	3 medium base,
<b>P2743-74</b>	Venetian Bronze		Extends 7-1/8".	each 100w max.
<b>P2745-09</b>	Brushed Nickel	Four-light	32-1/8" W., 9" ht.	4 medium base,
<b>P2745-74</b>	Venetian Bronze		Extends 7-1/8".	each 100w max.

See pages 62-63 for more of the North Park collection





P3184-09

**P3184-09** Brushed Nickel  
Two-light close-to-ceiling.  
Size: 14-5/8" dia., 7-1/8" ht.  
Lamps: Two medium base  
lamps, each 100w max.  
Damp location listed.

# Torino

Elegant rectangular scrolled arms and etched white glass complement the transitional bath.

Mounts up or down.

Damp location listed.



*Mount up*

P2884-09



*or down*

P2883-09



P2882-09



P2881-09



P2881-09

Product No.	Finish	Description	Size	Lamp(s)
<b>P2881-09</b>	Brushed Nickel	One-light	7" W., 8-1/4" ht. Extends 9-1/4".	1 medium base, 100w max.
<b>P2882-09</b>	Brushed Nickel	Two-light	16" W., 7-5/8" ht. Extends 9-1/4".	2 medium base, each 100w max.
<b>P2883-09</b>	Brushed Nickel	Three-light	25" W., 7-5/8" ht. Extends 9-1/4".	3 medium base, each 100w max.
<b>P2884-09</b>	Brushed Nickel	Four-light	34" W., 7-5/8" ht. Extends 9-1/4".	4 medium base, each 100w max.

See pages 66-67 for more of the Torino collection



# Kensington

Traditionally-rooted collection featuring scrolled arms with trumpet-shaped glass shades in a swirl flute with frosted caramel finish.

Available in Forged Bronze.

Mounts up or down.

Damp location listed.



P2783-77



P2783-77



P3829-77

**P3829-77** Forged Bronze  
Two-light semi-flush.  
Size: 14" dia., 12" ht.  
Lamps: Two medium base lamps, each 100w max.



P2784-77



P2785-77

Product No.	Finish	Description	Size	Lamp(s)
<b>P2783-77</b>	Forged Bronze	One-light	6" W., 9-1/2" ht. Extends 7".	1 medium base, 100w max.
<b>P2784-77</b>	Forged Bronze	Two-light	15" W., 9-1/2" ht. Extends 7-5/8".	2 medium base, each 100w max.
<b>P2785-77</b>	Forged Bronze	Three-light	24-1/8" W., 9-1/2" ht. Extends 7-5/8".	3 medium base, each 100w max.

See pages 50-51 for more of the Kensington collection



# Janos

Simplistic arms and modern vessel glass shades in a soft etched finish create a minimalist urban feel.

Offered in Brushed Nickel.

Mounts up or down.

Damp location listed.

**P3855-09** Brushed Nickel  
Two-light semi-flush.  
Size: 13-3/8" dia., 8-3/8" ht.  
Lamps: Two medium base  
lamps, each 100w max.



P3855-09



P2908-09



P2908-09



P2909-09



P2911-09

See pages 52-53 for more of the Janos collection



Product No.	Finish	Description	Size	Lamp(s)
P2908-09	Brushed Nickel	One-light	6" W., 9" ht. Extends 8-1/2".	1 medium base, 100w max.
P2909-09	Brushed Nickel	Two-light	15-1/4" W., 8-5/8" ht. Extends 8-1/2".	2 medium base, each 100w max.
P2911-09	Brushed Nickel	Three-light	24-1/2" W., 8-5/8" ht. Extends 8-1/2".	3 medium base, each 100w max.



# Westin CFL

Incorporating a minimalist design style, this award-winning collection represents a shift in trends to highlight a less complicated, clean design.

Energy Star rated.

Title 24 compliant.

Mounts up or down.

Damp location listed.

**P3290-09EBWB** Brushed Nickel  
**P3290-20EBWB** Antique Bronze  
 Two-light close-to-ceiling.  
 Size: 14" dia., 7" ht.  
 Lamps: Two 13w CFL, included.  
 GU24 base.



P3290-09EBWB



P3290-20EBWB

P2794-20EBWB



P2794-09EBWB



*One-light*

*or three-light*



P2796-20EBWB



P2796-09EBWB

Product No.	Finish	Description	Size	Lamp(s)
<b>P2794-09EBWB</b>	Brushed Nickel	One-light	4-3/4" W., 8-1/4" ht.	1 13w CFL. GU24 base. included
<b>P2794-20EBWB</b>	Antique Bronze	One-light	4-3/4" W., 8-1/4" ht. Extends 6-1/4".	1 13w CFL. GU24 base. included
<b>P2796-09EBWB</b>	Brushed Nickel	Three-light	21" W., 8-1/4" ht.	3 13w CFL. GU24 base. included
<b>P2796-20EBWB</b>	Antique Bronze	Three-light	21" W., 8-1/4" ht. Extends 6-1/4".	3 13w CFL. GU24 base. included



See pages 57-59 for more of the Westin CFL collection



Title 24  
Compliant 

# Brushed Nickel or Antique Bronze

Simple transitional design with elongated racetrack-style backplate. Etched alabaster glass shades.

Energy Star rated.

Title 24 compliant.

Mounts up or down.

Damp location listed.



*Energy-efficient  
and stylish too*



Product No.	Finish	Description	Size	Lamp(s)	
<b>P3051-09EBWB</b>	Brushed Nickel	One-light	5-1/4" W., 9" ht.	1 13w spiral CFL.	
<b>P3051-20EBWB</b>	Antique Bronze		Extends 7-1/4".	GU24 base, included	
<b>P3052-09EBWB</b>	Brushed Nickel	Two-light	18" W., 7-1/4" ht.	2 13w spiral CFL.	
<b>P3052-20EBWB</b>	Antique Bronze		Extends 7-1/4".	GU24 base, included	
<b>P3053-09EBWB</b>	Brushed Nickel	Three-light	24" W., 7-1/4" ht.	3 13w spiral CFL.	
<b>P3053-20EBWB</b>	Antique Bronze		Extends 7-1/4".	GU24 base, included	
<b>P3054-09EBWB</b>	Brushed Nickel	Four-light	30" W., 7-1/4" ht.	4 13w spiral CFL.	
<b>P3054-20EBWB</b>	Antique Bronze		Extends 7-1/4".	GU24 base, included	



# Linear Fluorescent Bath




Etched glass.

Energy Star rated.


Title 24 compliant.

Damp location listed.

Product No.	Finish	Description	Size	Lamp(s)
<b>P7211-09</b>	Brushed Nickel	One-light w/etched glass	25-5/8" W., 5-1/4" ht. Extends 4".	1 17w T8
<b>P7212-09</b>	Brushed Nickel	One-light w/etched glass	37-5/8" W., 5-1/4" ht. Extends 4".	1 25w T8



P7211-09



P7212-09

# Maier

Energy Efficient CFL



Clean and simple cylinder silhouettes in a Brushed Nickel finish with white satin acrylic shade for an urban loft styling.

Title 24 compliant.

Damp location listed.

Product No.	Finish	Description	Size	Lamp(s)
<b>P2926-09</b>	Brushed Nickel w/white acrylic	One-light	5" W., 10-5/8" ht. Extends 4-3/4". H/CTR 8-1/8".	1 18w CFL, GU24 base.
<b>P7025-09</b>	Brushed Nickel w/white acrylic	Two-light	28-1/8" W., 5" ht. Extends 5". H/CTR 2-1/2".	2 24w 4-pin CFL, 2G11 base.



P7025-09

*mount horizontally*

See page 78 for Maier close-to-ceiling fixtures.



P2926-09

P2926-09

*mount up  
or down*



P7025-09

*or vertically*

# EnergyStar Bath Fans

The PV020-30 and PV021-30 are Energy Star qualified bath fans that offer the best combination of energy efficiency and quiet operation. Both models are rated for 80CFM air flow at 0.1" Ps accommodating 72ft<sup>2</sup> rooms with 8' ceiling heights, and have sound ratings ≤1 sone. Air and sound ratings have been verified and listed by the Home Ventilating Institute.

Motors are encased and permanently lubricated for continuous operation. Diffusers are white, and are retained by torsion springs to ensure a tight fit against the ceiling and easy installation. Both models accommodate 2" x 8" joist construction, and are shipped with bar hangers that can be adjusted for 24" joist spans.

The PV021 model is a lighted bath fan and is shipped with a 13W GU24 2700K CCT lamp.



PV020-30

**PV020-30** Textured White  
80 cfm bath fan  
Recommended bath size 75 sq. ft.  
Sound level rating 0.7 Sones  
4" duct fitting  
Grille size: 12-3/4" sq., 7/8" deep  
Back box: 9-1/4" L., 11-5/8" W.,  
8" ht.  
cULus listed




PV021-30

**PV021-30WB** Textured White  
80 cfm bath fan with light  
Recommended bath size 75 sq. ft.  
Sound level rating 1.0 Sones  
4" duct fitting  
Grille size: 21-5/8" sq., 4" deep  
Back box: 9-1/4" L., 11-5/8" W.,  
8" ht.  
Lamp: One 13w GU24, 2700K  
(included)  
cULus listed



## Channel Glass

Product No.	Finish	Description	Size	Lamp(s)
P3111-30	White Glass	Two-light. K.O. for switch.	13" W., 4-1/4" ht. Extends 4-1/4".	2 medium base, each 75w max.
P3110-30	White Glass	Four-light. K.O. for switch.	24" W., 4-1/4" ht. Extends 4-3/4".	4 medium base, each 75w max.



P3110-30



P3111-30



# Le Papier

Progress Lighting is pleased to announce the release of an innovative series of ADA sconces that optimize value in aesthetic appeal through decorative element options, and energy savings by utilizing the high efficiency of compact fluorescent lamps. These sconces can be used in either commercial or residential applications.

The outer diffuser is an extruded acrylic element that offers a smooth, finished appeal, and high transmissivity. An inner transmissive element diffuses the CFL light source to provide even luminance. The primary aesthetic element is decorative hand made paper in optional patterns and colors. End Caps allow luminance below and above the fixture, and include decorative elements available in both nickel and bronze finishes.



P7217-30

**P7217-30** White  
Chassis for sconces.  
Size: 6" W., 10-1/8" ht.  
Extends 2-7/8".  
Lamps: One 26w CFL,  
GU24 base.



P7003-20RP



P7003-09NP

**P7003-09NP** Brushed Nickel  
**P7003-20NP** Antique Bronze  
Lokta Oil Sticks paper.  
Size: 10-1/2" W., 12-1/4" ht.  
Extends 4".  
ADA



P7003-20NP



P7003-09RP

**P7003-09RP** Brushed Nickel  
**P7003-20RP** Antique Bronze  
Mango Brick paper.  
Size: 10-1/2" W., 12-1/4" ht.  
Extends 4".  
ADA



P7003-09GP



P7003-20GP

**P7003-09GP** Brushed Nickel  
**P7003-20GP** Antique Bronze  
Raintree Leaves Green/Gold  
paper.  
Size: 10-1/2" W., 12-1/4" ht.  
Extends 4".  
ADA



Le Papier sponce diffuser



P7003-09SP



P7003-20SP

**P7003-09SP** Brushed Nickel  
**P7003-20SP** Antique Bronze  
Stonehenge paper.  
Size: 10-1/2" W., 12-1/4" ht.  
Extends 4".  
ADA.

# Le Papier



P7003-09WP



P7003-20WP

**P7003-09WP** Brushed Nickel  
**P7003-20WP** Antique Bronze  
Whimsy White paper.  
Size: 10-1/2" W., 12-1/4" ht.  
Extends 4".  
ADA



P7003-09BP

**P7003-09BP** Brushed Nickel  
**P7003-20BP** Antique Bronze  
Banana Blue paper.  
Size: 10-1/2" W., 12-1/4" ht.  
Extends 4".  
ADA






P7003-20BP

# How to order Le Papier Sconces

Specify a chassis and a paper diffuser with either nickel or bronze accent.

## Step 1: Chassis

Start with the chassis P7217-30, featuring a GU24 lamp base. GU24 base lamps provide for options in color temperature, wattage and dimming. Maximum wattage is 26w. The GU24 base provides for options in color temperature, wattage and dimming. (Lamp purchased separately)




P7217-30 Chassis shown with CFL lamp (purchased separately)

## Step 2: Select a paper diffuser

Choose from a broad range of fabrics with either Brushed Nickel (-09) or Antique Bronze (-20) end caps.



P7003-09BP / P7003-20BP  
Banana Blue paper



P7003-09RP / P7003-20RP  
Mango Brick paper



P7003-09GP / P7003-20GP  
Raintree Leaves Green/Gold paper



P7003-09NP / P7003-20NP  
Lokta Oil Sticks paper




P7003-09SP / P7003-20SP  
Stonehenge paper.



P7003-09WP / P7003-20WP  
Whimsy White paper

## Completed Sconce: Chassis + Paper Diffuser



Brushed Nickel endcaps



Antique Bronze endcaps





# Outdoor CFL Wall Sconces



Energy efficient CFLs

Title 24 compliant

## Parker

Versatile wall sconce can be used indoor and outdoor. Top and bottom can be removed for indoor use as a wall sconce.


**P5914-16** Satin Aluminum  
**P5914-20** Antique Bronze  
 One-light CFL wall sconce. White acrylic diffuser.  
 Size: 5-3/8" W., 10-1/4" ht. Extends 4".  
 Lamp: One 26w CFL. GU24 base.  
 Wet location listed  
 ADA



P5914-16




P5914-20



P5914-20  
 shown without top and bottom for interior use.

**P5915-16** Satin Aluminum  
**P5915-20** Antique Bronze  
 Two-light CFL wall sconce. White acrylic diffuser.  
 Size: 5-3/8" W., 16-7/8" ht. Extends 4".  
 Lamps: Two 26w CFL. GU24 base.  
 ADA



P5915-16



P5915-20

## Shelton

**P5790-09** Brushed Nickel  
 One-light CFL wall sconce. White acrylic diffuser. Can be mounted vertically or horizontally. Can be used indoors or outdoors.  
 Size: 11" W., 5-5/8" ht. Extends 3-3/4".  
 Lamp: One 13w 4-pin CFL. GX24q-3 base.  
 Wet location listed.  
 ADA



P5790-09



P5790-09

## Maier

**P5746-09** Brushed Nickel  
 One-light wall lantern torchiere, style. White acrylic shade. Mounts in up position only.  
 Size: 5" W., 10-5/8" ht. Extends 4-3/4". H/CTR 8-1/8".  
 Lamp: One 26w spiral CFL. GU24 base.



P5746-09



## Anson

**P5736-09** Brushed Nickel  
**P5736-129** Architectural Bronze  
 One-light CFL wall sconce. Can be used indoors or outdoors.  
 Size: 9-1/8" W., 10-1/4" ht. Extends 3-3/4". H/CTR 5-5/8".  
 Lamp: One 18w spiral CFL. GU24 base.  
 Wet location listed.  
 ADA



P5736-09



P5736-129

## Valera

**P5800-09** Brushed Nickel  
**P5800-20** Antique Bronze  
 One-light CFL wall lantern.  
 Size: 5-5/8" W., 8-1/8" ht. Extends 4".  
 Lamp: One 18w CFL. GU24 base.



P5800-09




P5800-20

**P5801-09** Brushed Nickel  
**P5801-20** Antique Bronze  
 One-light CFL wall lantern.  
 Size: 8-1/8" W., 11-1/8" ht. Extends 4".  
 Lamp: One 26w CFL. GU24 base.



P5801-09



P5801-20



P5806-09



P5806-20

**P5806-09** Brushed Nickel  
**P5806-20** Antique Bronze  
 Two-light CFL wall lantern.  
 Size: 5-5/8" W., 16-1/8" ht. Extends 4".  
 Lamps: Two 18w CFL. GU24 base.

Title 24  
Compliant



Energy  
Efficient CFL



# Meadowlark

Casual European styled lanterns.

Unique arched roof and top ribbon scrolled loops, with arching arms and shepherd's crook.

Water seeded glass.

Oil Rubbed Bronze finish.

*water seeded glass*



*Water seeded glass*

P5502-108



**P5502-108** Oil Rubbed Bronze  
Three-light hanging lantern.  
Size: 8-1/2" W., 6-7/8" L., 15" ht.  
Overall ht. w/chain 90", wire 15".  
Lamps: Three candelabra base  
lamps, each 60w max.  
Damp location listed.

*arched roof*



P5715-108

**P5715-108** Oil Rubbed Bronze  
One-light wall lantern.  
Size: 6-3/8" W., 12" ht.  
Extends 6-7/8". H/CTR 7-5/8".  
Lamp: One medium base lamp,  
100w max.

**P5716-108** Oil Rubbed Bronze  
Two-light wall lantern.  
Size: 7-1/4" W., 14-1/2" ht.  
Extends 8-1/4". H/CTR 7-3/4".  
Lamps: Two candelabra base  
lamps, each 60w max.



P5716-108

*Oil Rubbed Bronze*



P5468-108

**P5468-108** Oil Rubbed Bronze  
Three-light post lantern.  
Size: 6-7/8" L., 8-1/2" W., 14-1/2" ht.  
Fits 3" post (order separately).  
Lamps: Three candelabra base  
lamps, each 60w max.



P5717-108

**P5717-108** Oil Rubbed Bronze  
Three-light wall lantern.  
Size: 8-1/2" W., 17-1/8" ht.  
Extends 9-5/8". H/CTR 9".  
Lamps: Three candelabra base  
lamps, each 60w max.

# Prestwick

Stately traditional style with classic roof lines and unique cast yoke straps.

Water glass urn shades.

Oil Rubbed Bronze finish.



P5920-108

**P5920-108** Oil Rubbed Bronze  
One-light wall lantern.  
Size: 6-7/8" W., 11" ht.  
Extends 8". H/CTR 5-1/4".  
Lamp: One medium base  
lamp, 100w max.



P5584-108

**P5584-108** Oil Rubbed Bronze  
Three-light hanging lantern.  
Size: 10-3/4" dia., 17-3/4" ht.  
Overall ht. w/chain 93", wire 15".  
Lamps: Three candelabra base  
lamps, each 60w max.  
Damp location listed.

*Oil Rubbed Bronze*



*Water glass*



P5923-108

**P5923-108** Oil Rubbed Bronze  
Three-light wall lantern.  
Size: 10-3/4" W., 16-3/4" ht.  
Extends 12". H/CTR 7-7/8".  
Lamps: Three candelabra base  
lamps, each 60w max.



P5921-108

**P5921-108** Oil Rubbed Bronze  
Two-light wall lantern.  
Size: 8-3/4" W., 13-7/8" ht.  
Extends 10". H/CTR 6-3/4".  
Lamps: Two candelabra base  
lamps, each 60w max.



P5484-108

*water glass urn shades*

**P5484-108** Oil Rubbed Bronze  
Three-light post lantern.  
Size: 10-3/4" dia., 18-3/4" ht.  
Fits 3" post (order separately).  
Lamps: Three candelabra base  
lamps, each 60w max.



# Montreux LED

European country manor style with cottage-casual undertones highlights this outdoor LED lantern series.

With Antique Bronze finish and clear-distressed glass, the environmentally responsible and energy efficient lanterns are perfect for outdoor entryway, garden settings, walkways and pathways.

PROGRESS **LED**

*state-of-the-art LEDs*



P5614-20

**P5614-20** Antique Bronze  
One-light 5w LED wall lantern.  
Size: 6" W., 9-1/8" ht.  
Extends 7-1/2". H/CTR 6-1/8".  
Lamp: One 5w LED included.



P5619-20

**P5619-20** Antique Bronze  
One-light 5w LED wall lantern.  
Size: 8" W., 11-5/8" ht.  
Extends 10-1/8". H/CTR 7-7/8".  
Lamp: One 5w LED included.



P5638-20

**P5638-20** Antique Bronze  
One-light 14w LED wall lantern.  
Size: 10" W., 14-1/8" ht.  
Extends 12-3/8". H/CTR 8-1/2".  
Lamp: One 14w LED included.



P5447-20

*clear distressed glass*

**P5447-20** Antique Bronze  
One-light 14w LED post lantern.  
Size: 10" sq., 19-1/4" ht.  
Fits 3" post (order separately).  
Lamp: One 14w LED included.

*Antique Bronze*

P5598-20STR



*antique  
distressed glass*



# Montreux CFL

CFL version features antique distressed glass and photocell.

Energy Star rated.

Title 24 compliant.

**P5598-20STR** Antique Bronze  
One-light CFL hanging lantern  
w/photocell (additional chain  
available).  
Size: 10" sq., 15-3/4" ht.  
Overall ht. w/chain 91", wire 15'.  
Lamp: One 26w CFL, GU24 base.  
Damp location listed.



P5655-20STR

**P5655-20STR** Antique Bronze  
One-light CFL wall lantern  
w/photocell.  
Size: 6" W., 9-1/8" ht. Extends  
7-1/2". H/CTR 6-1/8".  
Lamp: One 13w CFL, GU24  
base.



P5514-20STR

**P5514-20STR** Antique Bronze  
Two-light CFL close-to-ceiling  
w/photocell.  
Size: 10-1/2" sq., 6-5/8" ht.  
Lamps: Two 13w CFL, GU24  
base.  
Damp location listed.



P5692-20STR

**P5692-20STR** Antique Bronze  
One-light CFL wall lantern  
w/photocell.  
Size: 8" W., 11-1/2" ht.  
Extends 5". H/CTR 7-1/8".  
Lamp: One 18w CFL,  
GU24 base.

*energy efficient CFLs*



P5498-20STR

**P5498-20STR** Antique Bronze  
One-light CFL post lantern  
w/photocell.  
Size: 10" sq., 19-1/4" ht.  
Fits 3" post (order separately).  
Lamp: One 26w CFL,  
GU24 base.



P5699-20STR

**P5699-20STR** Antique Bronze  
One-light CFL wall lantern  
w/photocell.  
Size: 10" W., 14-1/8" ht.  
Extends 12-3/8". H/CTR 8-1/2".  
Lamp: One 26w CFL,  
GU24 base.



P5599-20STR

**P5599-20STR** Antique Bronze  
One-light CFL wall lantern  
w/photocell.  
Size: 8" W., 11-5/8" ht.  
Extends 10-1/8". H/CTR 7-7/8".  
Lamp: One 26w CFL,  
GU24 base.

# Westport CFL



With casual, comfortable outdoor settings more popular than ever, this classic design incorporates beaded detailing in die-cast aluminum and etched seeded glass.

Energy Star rated.

Title 24 compliant.

**P5530-20STR** Antique Bronze  
One-light CFL hanging lantern w/photocell (additional chain available).  
Size: 9" dia., 14-3/4" ht.  
Overall ht. w/chain 90", wire 15'.  
Lamp: One 13w CFL, GU24 base.  
Damp location listed.



P5530-20STR

P3883-20STR



**P3883-20STR** Antique Bronze  
One-light CFL close-to-ceiling w/photocell.  
Size: 9" dia., 10-1/2" ht.  
Lamp: One 13w CFL, GU24 base.  
Damp location listed.

*etched  
seeded  
glass*



P5864-20STR

**P5864-20STR** Antique Bronze  
One-light CFL wall lantern w/photocell.  
Size: 11" W., 19-1/2" ht.,  
Extends 12-7/8", H/CTR 4-5/8".  
Lamp: One 18w CFL, GU24 base.



P5863-20STR

**P5863-20STR** Antique Bronze  
One-light CFL wall lantern w/photocell.  
Size: 9" W., 16" ht.,  
Extends 10-3/8". H/CTR 3-1/2".  
Lamp: One 13w CFL, GU24 base.



P5862-20STR

**P5862-20STR** Antique Bronze  
One-light CFL wall lantern w/photocell.  
Size: 6-7/8" W., 12-3/4" ht.,  
Extends 8-3/8". H/CTR 3-1/4".  
Lamp: One 13w CFL, GU24 base.



**P5434-20STR** Antique Bronze  
One-light CFL post lantern w/photocell.  
Size: 11" dia., 19" ht.  
Fits 3" post (order separately).  
Lamp: One 18w CFL, GU24 base.

P5434-20STR

*energy efficient*



# Westport

Clear seeded glass.

Antique Bronze finish.

**P5530-20** Antique Bronze  
One-light hanging lantern.  
Size: 9" dia., 14-3/4" ht.  
Overall ht. w/chain 90", wire 15'.  
Lamp: One medium base lamp,  
100w max.  
Damp location listed



P5530-20

P3883-20



**P3883-20** Antique Bronze  
One-light close-to-ceiling.  
Size: 9" dia., 10-1/2" ht.  
Lamp: One medium base lamp,  
100w max.  
Damp location listed.

*Antique Bronze*



P5864-20

**P5864-20** Antique Bronze  
Two-light wall lantern.  
Size: 11" W., 19-1/2" ht;  
Extends 12-7/8". H/CTR 4-5/8".  
Lamps: Two candelabra base  
lamps, each 60w max.



P5863-20

**P5863-20** Antique Bronze  
One-light wall lantern.  
Size: 9" W., 16" ht.  
Extends 10-3/8". H/CTR 3-1/4".  
Lamp: One medium base lamp,  
100w max.



P5862-20

**P5862-20** Antique Bronze  
One-light wall lantern.  
Size: 6-7/8" W., 12-3/4" ht.  
Extends 8-3/8". H/CTR 3-1/4".  
Lamp: One medium base lamp,  
60w max.

*clear  
seeded  
glass*



P5434-20

**P5434-20** Antique Bronze  
Two-light post lantern.  
Size: 11" dia., 19" ht.  
Fits 3" post (order separately).  
Lamps: Two candelabra base  
lamps, each 60w max.



# BrassGuard Lanterns

Clear beveled glass in a classic Black finish.

*clear beveled glass*

**P5731-31** Black  
Three-light wall lantern.  
Size: 9-3/4" W., 33" ht.  
Extends 9-1/2". H/CTR 20-1/2".  
Lamps: Three candelabra base  
lamps, each 60w max.



P5731-31



P5831-31

**P5831-31** Black  
One-light wall lantern.  
Size: 7-1/8" W., 28-1/2" ht.  
Extends 7-5/8". H/CTR 16".  
Lamp: One medium base  
lamp, 100w max.



P5758-31

**P5758-31** Black  
One-light wall lantern.  
Size: 5-3/8" W., 18-3/4" ht.  
Extends 5-5/8". H/CTR 7-1/4".  
Lamp: One medium base  
lamp, 100w max.



P5432-31

**P5432-31** Black  
Three-light post lantern.  
Size: 9-3/4" dia., 21-1/4" ht.  
Fits 3" post (order separately).  
Lamps: Three candelabra base  
lamps, each 60w max.

*Basic Black*

P5846-31

**P5846-31** Black  
One-light wall lantern.  
Size: 5-1/4" W., 14-3/4" ht.,  
Extends 6". H/CTR 8-3/8".  
Lamp: One medium base  
lamp, 60w max.



P5756-31

**P5756-31** Black  
One-light wall lantern.  
Size: 5-3/8" W., 10-1/4" ht.  
Extends 5-5/8". H/CTR 3-3/4".  
Lamp: One medium base  
lamp, 100w max.



## Milford CFL Lanterns

Classic wall lanterns with transitional styling.  
Antique Bronze, White or Black finish with  
matte white acrylic diffuser.

Energy  
Efficient CFL



P5821-20



P5821-30



P5821-31

**P5821-20** Antique Bronze  
**P5821-30** White  
**P5821-31** Black  
One-light wall lantern.  
Size: 5-3/4" W., 8-3/4" ht.  
Extends 4-5/8", H/CTR 5-1/8".  
Lamp: One 13w CFL. GU24 base.

*energy efficient CFLs*

# Surface Mount LED

The P8022 is a surface mount LED downlight with light output and distribution that rivals that of typical 65W BR30 incandescents but at only 13w of input power. Intended for use in both new construction and remodel, the P8022 is ideal for single and multi-family applications such as utility and general illumination. This product is available in both warm white 2700K (incandescent) and 3500K (halogen) correlated color temperatures, and the -30 gloss white trim finish.

The regressed internal reflector is designed to enhance performance while also diffusing the LED sources. The acrylic lens diffuses the LED's effectively creating a single visible source. The soft profile of the outer housing is designed to blend into the ceiling.

Installation accommodates both new construction and remodel applications and requires direct mount to standard junction boxes. The mounting strap is first secured to the junction box. Then two screws are driven through the side of the housing into the strap creating a snug fit to the ceiling. This pulls the housing flush to the ceiling to eliminate gaps and light leaks.

The P8022 is cULus classified for use in damp locations. Warranty is 3 years. Anticipated life is 50,000 hours L70. This means that at 50,000 hours, the LED's will be providing 70% of initial lumens

The P8022 can be considered as an option to recessed, especially in applications where fire codes must be followed.



**P8022-30** White, 2700K color temperature  
**P8022-30/35K** White, 3500K color temperature  
8" surface mount LED trim.  
Size: 1-3/4" ht., 8" overall diameter  
13-watt input power  
9 LED (light emitting diodes) included.



# About Progress LED Recessed

## High Lumen Output

The P8071 6" trim has lumen output and distribution comparable to a 65W BR30 incandescent lamp.

## Long Life

Anticipated life is 50,000 hours. This is based on 70% lumen maintenance. An average incandescent has a life of 800-2,000 hours and the average CFL 6,000-12,000 hours.

## Warm White Color

Significant increases in efficacy and warm white color consistency. Available in both warm white 2700K (incandescent) and 3500K (halogen) color temperatures.

## Superior Dimming

Dimmable to 20 percent of full output on 3-wire low voltage electronic dimmer switches on 2-wire circuits. Most self-ballasted CFLS are not dimmable at all.

## Aesthetic Appeal

Acrylic lens diffuses the diode light source to effectively create a single visible source. Regressed reflector and minimal optical aperture create significantly reduced glare, resulting in improved quality of light.



# LED Recessed for New Construction, Remodel and Retrofit

## Options for New Construction, Remodel and Retrofit

Intended for use in both new construction and remodel applications.

Easy installation and UL classification for use with Progress and competitors recessed cans make Progress LED trims ideal for retrofitting.

## Compatible with Competitive Recessed Housings


Progress LED standard trims are UL classified for use with many competitive recessed cans, including models from Capri, Commercial Electric, Emerald, Elco, Halo, Intense, Jimway, Juno, Luminaire, LumaPro, Lithonia, Nora, Sea Gull, and WAC.

## Quick-Link Solutions for Title 24 Applications


Quick-Link (QL) trims comply with California Title 24 requirements for providing a plug-in power connector in place of a screw shell socket.



Progress LED Quick-Link trims are designed to comply with building codes, including California Title 24, where use of screw shell sockets is restricted. Quick-Link trims are compatible with correlated Quick-Link housings from Progress Lighting.



## LED Recessed Trim Anatomy





# P8071 6" & P8026 4" LED Trims

**Single Solution Trims** These LED trims are ideal for both new and remodel residential and light commercial construction.

**Easy installation** with (3) friction spring clips.

**Universal screw shell lamp adapter** Compatible with many competitive recessed housings.

**High Lumen Output** P8071 6" trims are comparable to a 65w BR30 incandescent lamp. P8026 4" trims are comparable to a 50w R20 incandescent lamp.

**Superior dimming capabilities** When used with 3-wire low voltage electronic dimmers on 2-wire circuits, these trims feature gradual dimming to 20% of full light output through the dimmer's full range.

**Aesthetic Appeal** Acrylic lens diffuses LEDs, effectively creating a single visible source.

**Regressed reflector** and minimal optical aperture create significantly reduced glare resulting in improved quality of light.

## P8071 6" LED Trims: IC/Non-IC, New Construction & Remodel



**P8071-20** Antique Bronze, 2700K color temp  
**P8071-20/35K** Antique Bronze, 3500K color temp



**P8071-28** White, 2700K color temp  
**P8071-28/35K** White, 3500K color temp



**P8071-31** Black, 2700K color temp  
**P8071-31/35K** Black, 3500K color temp



**P8071-36** Chestnut, 2700K color temp  
**P8071-36/35K** Chestnut, 3500K color temp



**P8071-121** Metallic Silver, 2700K color temp  
**P8071-121/35K** Metallic Silver, 3500K color temp

### P8071 6" LED TRIM

9 LED (Light Emitting Diode) lamps included

12-watt input power

Lumen output: 584 lumens (3500K), 502 lumens (2700K)

CRI is 73

Lamp contains no mercury, meets California Title 22 requirements

12W 6" recessed LED trim  
 Smooth lensed trim with integral flange  
 Output: 502 lm (2700K), 584 lm (3500K)  
 UL/CUL classified for wet locations  
 Dimensions: 5" ht., 7-3/4" overall dia.

## P8026 4" LED Trims: IC/Non-IC, New Construction & Remodel



**P8026-20** Antique Bronze, 2700K color temp  
**P8026-20/35K** Antique Bronze, 3500K color temp



**P8026-28** White, 2700K color temp  
**P8026-28/35K** White, 3500K color temp



**P8026-31** Black, 2700K color temp  
**P8026-31/35K** Black, 3500K color temp



**P8026-36** Chestnut, 2700K color temp  
**P8026-36/35K** Chestnut, 3500K color temp



**P8026-121** Metallic Silver, 2700K color temp  
**P8026-121/35K** Metallic Silver, 3500K color temp

### P8026 4" LED TRIM

9 LED (Light Emitting Diode) lamps included

11-watt input power

Lumen output: 517 lumens (3500K), 434 lumens (2700K)

CRI is 75+

Lamp contains no mercury, meets California Title 22 requirements

cULus listed for wet locations

11W 4" recessed LED retrofit trim  
 Smooth lensed trim with integral flange  
 Output: 434 lm (2700K), 517 lm (3500K)  
 UL/CUL classified for wet locations  
 Dimensions: 4" ht., 5" overall dia.

# P8071 6" & P8026 4" Quick-Link Trims

**Single Solution Trims** These QL trims are ideal for new construction residential and light commercial applications.

**California Title 24 Compliant** Provides a power connector in place of screw shell socket.

**High Lumen Output** P8071 6" trims are comparable to a 65w BR30 incandescent lamp. P8026 4" trims are comparable to a 50w R20 incandescent lamp.



**Superior dimming capabilities** When used with 3-wire low voltage electronic dimmers on 2-wire circuits, these trims feature gradual dimming to 20% of full light output through the dimmer's full range.

**Enhanced appearance** Acrylic lens diffuses the LEDs, effectively creating a single visible source.

**Regressed reflector** and minimal optical aperture create significantly reduced glare resulting in improved quality of light.

## P8071 6" Quick-Link LED Trims: IC/Non-IC, New Construction & Retrofit



**P8071 6" Quick-Link LED Trim**  
 9 LED (Light Emitting Diode) lamps included  
 12-watt input power  
 Quick Link power coupler  
 Lamp contains no mercury, meets California Title 22 requirements  
 cULus listed for wet locations  
 Works with P87-ATQL housing (ordered separately)



**P8071-20QL/27K** Antique Bronze, 2700K color temp  
**P8071-20QL/35K** Antique Bronze, 3500K color temp



**P8071-28QL/27K** White, 2700K color temp  
**P8071-28QL/35K** White, 3500K color temp



**P8071-31QL/27K** Black, 2700K color temp  
**P8071-31QL/35K** Black, 3500K color temp



**P8071-36QL/27K** Chestnut, 2700K color temp  
**P8071-36QL/35K** Chestnut, 3500K color temp



**P8071-121QL/27K** Metallic Silver, 2700K color temp  
**P8071-121QL/35K** Metallic Silver, 3500K color temp

**12W 6" recessed LED Quick-Link trim**  
 Smooth lensed trim with integral flange  
 Output: 502 lm (2700K), 584 lm (3500K)  
 Dimensions: 5" ht., 7-3/4" overall dia.



**P87-ATQL 6" Recessed New Construction Housing**  
 Integral nail bar hanger  
 Dimensions: 7-7/8" x 10-3/4"  
 Ceiling opening: 6-7/8" dia.  
 Plaster frame: 7-7/8" x 10-3/4"  
 Recessed depth: 7-1/2"  
 Pryouts: 1/2" & 3/4"  
 UL and CUL listed for damp locations

## P8026 4" Quick-Link LED Trims: IC/Non-IC, New Construction & Retrofit



**P8026 4" Quick-Link LED Trim**  
 9 LED (Light Emitting Diode) lamps included  
 11-watt input power  
 Quick Link power coupler  
 Lumen output: 517 lumens (3500K), 434 lumens (2700K)  
 CRI is 75+  
 Lamp contains no mercury, meets California Title 22 requirements  
 Works with P830-ATQL housing (ordered separately)



**P8026-20QL/27K** Antique Bronze, 2700K color temp  
**P8026-20QL/35K** Antique Bronze, 3500K color temp



**P8026-28QL/27K** White, 2700K color temp  
**P8026-28QL/35K** White, 3500K color temp



**P8026-31QL/27K** Black, 2700K color temp  
**P8026-31QL/35K** Black, 3500K color temp



**P8026-36QL/27K** Chestnut, 2700K color temp  
**P8026-36QL/35K** Chestnut, 3500K color temp



**P8026-121QL/27K** Metallic Silver, 2700K color temp  
**P8026-121QL/35K** Metallic Silver, 3500K color temp

**11W 4" recessed LED Quick-Link trim**  
 Smooth lensed trim with integral flange  
 Output: 434 lm (2700K), 517 lm (3500K)  
 UL/CUL listed for wet locations  
 Dimensions: 4" ht., 5" overall dia.



**P830-ATQL 4" Recessed New Construction Housing**  
 Integral nail bar hanger  
 Ceiling opening: 4-1/2" dia.  
 Plaster frame: 7-7/8" x 10-3/4"  
 Recessed depth: 5-1/2"  
 Pryouts: 1/2" & 3/4"  
 UL and CUL listed for damp locations

# Accessories

## 9-GAUGE CHAIN



P8757-104

10 feet of 9 gauge chain permits installation of large chain-hung fixtures on high ceilings. Maximum fixture weight – 50 lbs.

**P8757-104** Polished Nickel  
**P8757-114** Weathered Auburn  
**P8757-124** Copper Bronze  
**P8757-126** Burnished Silver  
**P8757-127** Burnished Ebony

## 6 GAUGE CHAIN



P8759-127

**P8759-127** Burnished Ebony  
 10 feet of 6 gauge chain permits installation of large chain-hung fixtures on high ceilings. Maximum fixture weight – 120 lbs.

## MINI-PENDANT STEM EXTENSION



P8601-124

**P8601-114** Weathered Auburn  
**P8601-124** Copper Bronze  
 For mini-pendants. Contains (2) 12" and (2) 15" sections.

## XENON LAMP



**P7807-01** replacement lamp  
 60w Krypton, E2, 120V

## CFL LAMP



**MLS13GUWW-128** 13w self-ballasted lamp. GU24 base.

## Socket Collar Tool – for use in installing glass shades

**P8637-01** Socket collar tool  
 The socket collar tool was designed to provide extra leverage and eliminate a loose fit when installing glass shades. Working like a wrench, the socket collar tool extends into the shade and tightens the socket ring, securing the shade in place, and can reverse to loosen the ring to remove the shade. This new accessory can be used on a variety of fixtures, including chandeliers, mini-pendants, sconces and wall brackets. For use on medium base lamp fixtures only.



**P8637-01**  
 Socket collar tool



Position shade over fixture



Install socket ring over shade socket collar



Hold socket collar tool by narrow end, open end facing down over socket ring



Fit bottom (open end) of socket collar tool over socket ring. Twist right until tight.



Shade secured in place.

# Index

<b>P2000</b>	<b>P3184</b> ..... 67, 75, 103	<b>P4209</b> ..... 7	<b>P5692</b> ..... 119
<b>P2500</b> ..... 83	<b>P3185</b> ..... 97	<b>P4210</b> ..... 9	<b>P5699</b> ..... 119
<b>P2502</b> ..... 82	<b>P3194</b> ..... 97	<b>P4238</b> ..... 51	<b>P5715</b> ..... 116
<b>P2529</b> ..... 83	<b>P3290</b> ..... 59, 78, 106	<b>P4365</b> ..... 70	<b>P5716</b> ..... 116
<b>P2530</b> ..... 81	<b>P3291</b> ..... 49, 75, 97	<b>P4383</b> ..... 40	<b>P5717</b> ..... 116
<b>P2532</b> ..... 80	<b>P3400</b> ..... 7	<b>P4384</b> ..... 43	<b>P5731</b> ..... 122
<b>P2533</b> ..... 82	<b>P3457</b> ..... 72, 79	<b>P4400</b> ..... 20	<b>P5736</b> ..... 115
<b>P2601</b> ..... 85	<b>P3458</b> ..... 72	<b>P4405</b> ..... 68	<b>P5746</b> ..... 114
<b>P2618</b> ..... 85	<b>P3459</b> ..... 72	<b>P4415</b> ..... 69	<b>P5756</b> ..... 123
<b>P2620</b> ..... 85	<b>P3460</b> ..... 73, 79	<b>P4416</b> ..... 66	<b>P5758</b> ..... 122
<b>P2645</b> ..... 67, 84	<b>P3462</b> ..... 79	<b>P4417</b> ..... 66	<b>P5790</b> ..... 114
<b>P2648</b> ..... 85	<b>P3463</b> ..... 24, 74	<b>P4418</b> ..... 69	<b>P5800</b> ..... 115
<b>P2649</b> ..... 56, 58, 84	<b>P3464</b> ..... 50	<b>P4419</b> ..... 67	<b>P5801</b> ..... 115
<b>P2653</b> ..... 84	<b>P3509</b> ..... 57	<b>P4421</b> ..... 19	<b>P5806</b> ..... 115
<b>P2710</b> ..... 64, 100	<b>P3532</b> ..... 51	<b>P4422</b> ..... 21	<b>P5821</b> ..... 123
<b>P2711</b> ..... 100	<b>P3597</b> ..... 63, 76	<b>P4423</b> ..... 42	<b>P5831</b> ..... 122
<b>P2712</b> ..... 100	<b>P3617</b> ..... 71	<b>P4424</b> ..... 48	<b>P5846</b> ..... 123
<b>P2715</b> ..... 98	<b>P3701</b> ..... 13	<b>P4426</b> ..... 49	<b>P5862</b> ..... 120, 121
<b>P2716</b> ..... 98	<b>P3720</b> ..... 39	<b>P4429</b> ..... 41	<b>P5863</b> ..... 120, 121
<b>P2723</b> ..... 30	<b>P3739</b> ..... 46, 74	<b>P4431</b> ..... 3	<b>P5864</b> ..... 120, 121
<b>P2729</b> ..... 9	<b>P3757</b> ..... 57	<b>P4435</b> ..... 59	<b>P5914</b> ..... 114
<b>P2733</b> ..... 102	<b>P3759</b> ..... 21, 74	<b>P4436</b> ..... 58	<b>P5915</b> ..... 114
<b>P2738</b> ..... 102	<b>P3795</b> ..... 38	<b>P4448</b> ..... 29	<b>P5920</b> ..... 117
<b>P2739</b> ..... 107	<b>P3816</b> ..... 78	<b>P4453</b> ..... 29	<b>P5921</b> ..... 117
<b>P2743</b> ..... 102	<b>P3817</b> ..... 78	<b>P4466</b> ..... 64	<b>P5923</b> ..... 117
<b>P2745</b> ..... 102	<b>P3824</b> ..... 69	<b>P4468</b> ..... 65	
<b>P2755</b> ..... 98	<b>P3827</b> ..... 10	<b>P4481</b> ..... 52	<b>P7000</b>
<b>P2756</b> ..... 98	<b>P3829</b> ..... 51, 74, 104	<b>P4482</b> ..... 53	<b>P7003</b> ... 110, 111, 112
<b>P2758</b> ..... 91, 92	<b>P3836</b> ..... 77, 91, 92	<b>P4483</b> ..... 52	<b>P7072</b> ..... 46
<b>P2759</b> ..... 91, 92	<b>P3843</b> ..... 68	<b>P4484</b> ..... 44	<b>P7100</b> ..... 39
<b>P2760</b> ..... 91, 92	<b>P3847</b> ..... 68	<b>P4485</b> ..... 46	<b>P7127</b> ..... 56
<b>P2761</b> ..... 43, 96	<b>P3852</b> ..... 63, 76, 102	<b>P4487</b> ..... 45	<b>P7153</b> ..... 73
<b>P2762</b> ..... 96	<b>P3854</b> ..... 63, 76, 102	<b>P4488</b> ..... 52	<b>P7181</b> ..... 67
<b>P2763</b> ..... 96	<b>P3855</b> ..... 53, 75, 105		<b>P7211</b> ..... 108
<b>P2764</b> ..... 96	<b>P3861</b> ..... 65, 75, 100	<b>P5000</b>	<b>P7212</b> ..... 108
<b>P2783</b> ..... 50, 104	<b>P3862</b> ..... 31, 75	<b>P5028</b> ..... 37	<b>P7217</b> ..... 110
<b>P2784</b> ..... 104	<b>P3863</b> ..... 76, 99	<b>P5075</b> ..... 48	<b>P7807</b> ..... 128
<b>P2785</b> ..... 104	<b>P3866</b> ..... 79	<b>P5091</b> ..... 73	
<b>P2794</b> ..... 106	<b>P3867</b> ..... 79	<b>P5101</b> ..... 25	<b>P8000</b>
<b>P2796</b> ..... 106	<b>P3869</b> ..... 48	<b>P5108</b> ..... 57	<b>P8026</b> ... 124, 126, 127
<b>P2799</b> ..... 26	<b>P3870</b> ..... 77, 87, 89	<b>P5133</b> ..... 25	<b>P8071</b> ..... 126, 127
<b>P2800</b> ..... 26	<b>P3883</b> ..... 120, 121	<b>P5135</b> ..... 61	<b>P8601</b> ..... 128
<b>P2801</b> ..... 99	<b>P3884</b> ..... 16	<b>P5141</b> ..... 50	<b>P8637</b> ..... 128
<b>P2802</b> ..... 99	<b>P3888</b> ..... 16	<b>P5144</b> ..... 66	<b>P8719</b> ..... 8
<b>P2803</b> ..... 99	<b>P3890</b> ..... 47	<b>P5153</b> ..... 69	<b>P8757</b> ..... 128
<b>P2804</b> ..... 99	<b>P3902</b> ..... 15	<b>P5155</b> ..... 39	<b>P8759</b> ..... 128
<b>P2846</b> ..... 87, 89	<b>P3903</b> ..... 15	<b>P5167</b> ..... 56	<b>P8762</b> ..... 15
<b>P2847</b> ..... 87, 89	<b>P3904</b> ..... 15	<b>P5168</b> ..... 64	<b>P8765</b> ..... 34, 36
<b>P2848</b> ..... 87, 89	<b>P3905</b> ..... 40, 74	<b>P5174</b> ..... 70	<b>P8766</b> ..... 33, 36
<b>P2849</b> ..... 20	<b>P3906</b> ..... 63	<b>P5175</b> ..... 44	<b>P8768</b> ..... 33, 36
<b>P2881</b> ..... 103	<b>P3907</b> ..... 61	<b>P5176</b> ..... 53	<b>P8772</b> ..... 8
<b>P2882</b> ..... 103	<b>P3908</b> ..... 27	<b>P5191</b> ..... 30	<b>P8820</b> ..... 34
<b>P2883</b> ..... 103	<b>P3909</b> ..... 21	<b>P5198</b> ..... 34	<b>P8821</b> ..... 34
<b>P2884</b> ..... 103	<b>P3910</b> ..... 78	<b>P5199</b> ..... 34	<b>P8822</b> ..... 33
<b>P2908</b> ..... 105	<b>P3911</b> ..... 78	<b>P5256</b> ..... 20	<b>P8823</b> ..... 33
<b>P2909</b> ..... 105	<b>P3917</b> ..... 31	<b>P5282</b> ..... 53	<b>P8824</b> ..... 33
<b>P2911</b> ..... 105	<b>P3918</b> ..... 64	<b>P5432</b> ..... 122	<b>P8825</b> ..... 33
<b>P2926</b> ..... 108	<b>P3919</b> ..... 53	<b>P5434</b> ..... 120, 121	
	<b>P3920</b> ..... 65	<b>P5447</b> ..... 118	<b>PV000</b>
		<b>P5468</b> ..... 116	<b>PV020</b> ..... 109
<b>P3000</b>	<b>P4000</b>	<b>P5484</b> ..... 117	<b>PV021</b> ..... 109
<b>P3052</b> ..... 107	<b>P4001</b> ..... 62	<b>P5498</b> ..... 119	
<b>P3053</b> ..... 107	<b>P4002</b> ..... 62	<b>P5502</b> ..... 116	<b>MLST3GUWW</b> ..... 128
<b>P3054</b> ..... 107	<b>P4003</b> ..... 60	<b>P5514</b> ..... 119	
<b>P3089</b> ..... 101	<b>P4004</b> ..... 60	<b>P5530</b> ..... 120, 121	
<b>P3090</b> ..... 101	<b>P4005</b> ..... 37	<b>P5584</b> ..... 117	
<b>P3091</b> ..... 101	<b>P4053</b> ..... 61	<b>P5598</b> ..... 119	
<b>P3110</b> ..... 109	<b>P4130</b> ..... 24	<b>P5599</b> ..... 119	
<b>P3111</b> ..... 109	<b>P4131</b> ..... 27	<b>P5614</b> ..... 118	
<b>P3135</b> ..... 95	<b>P4132</b> ..... 26	<b>P5619</b> ..... 118	
<b>P3136</b> ..... 95	<b>P4158</b> ..... 50	<b>P5638</b> ..... 118	
<b>P3137</b> ..... 95	<b>P4208</b> ..... 8	<b>P5655</b> ..... 119	
<b>P3183</b> ..... 49, 97			

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL Listed or Classified or CSA Certified unless otherwise noted.

Thomasville Lighting® is manufactured by Progress Lighting under a license from and to the quality and design specifications of Thomasville Furniture Industries, Inc.

Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2010

All rights reserved.  
International Copyright Secured.



See Progress Lighting's full line catalog for additional fixtures.





Progress Lighting, Inc.

701 Millennium Boulevard  
Greenville, SC 29607  
[www.progresslighting.com](http://www.progresslighting.com)

1/10



Hubbell Lighting, Inc.