



**MEGAPRO<sup>®</sup>**  
Every bit better.

## Introducing LH Dottie's expanded line of MegaPro Screwdrivers and Accessories for the Professional Contractor



***New Drivers - New Bits - New Merchandisers***




**MEGAPRO<sup>®</sup>**  
Every bit better.

**New Special Drivers**

## Tamper Proof 2

- Tamper Proof 2 Driver features the newest selection of Security Bit Drivers:
- Tri-Wing, Torq-Set and Torq Plus



## ShaftLOC

- ShaftLOC features Locking Bits and Available Locking Extensions
- Extensions are available in 6" and 10" lengths
- ShaftLOC with Patent Pending locking bits will pass through a 3/8" dia. Opening


























**MEGAPRO**  
Every bit better.

# Bit Loads

<b>ORIGINAL</b> OUR MOST POPULAR 15:1 TOOL!	<b>BIT LOAD</b> 0 1 2 3 0 1 2 3 4 6 10 15 20 25 1/4" HEX SHAFT
<b>RATCHETING</b>	<b>BIT LOAD</b> 0 1 2 3 1 2 4 6 10 15 20 25 1/4" HEX SHAFT
<b>TAMPERPROOF</b> SECURITY BITS	<b>BIT LOAD</b> 1/8 9/64 5/32 3/16 6 8 10 12 10 15 20 25 27 30 1/4" HEX SHAFT
<b>TAMPERPROOF 2</b> SECURITY BITS	<b>BIT LOAD</b> 2 3 4 5 4 6 8 10 10 15 20 25 27 30 1/4" HEX SHAFT
<b>STAINLESS STEEL</b> ELECTROLESS NICKEL PLATED BITS	<b>BIT LOAD</b> 0 1 2 3 0 1 2 3 4 6 10 15 20 25 1/4" HEX SHAFT
<b>SHAFTLOK 15:1</b> STANDARD	<b>BIT LOAD</b> 0 1 2 3 0 1 2 3 4 6 10 15 20 25 1/4" HEX SHAFT
<b>HVAC</b>	<b>BIT LOAD</b> 0 1 2 2 2 3 SQUARE AWL 3 5 VALVE STEM 5.5 4 6 1/4" HEX SHAFT
<b>SPECIAL EDITION</b> PL ROBERTSON Bits	<b>BIT LOAD</b> 0 1 2 3 4 6 0 0 1 1 2 2 3 3 1/4" HEX SHAFT
<b>compact</b> STAINLESS STEEL	<b>BIT LOAD</b> 1 2 1 2 4 6 1/4" HEX SHAFT






























<b>MEGALOK</b> LOCKING QUICK CHANGE CRUISE	<b>BIT LOAD</b> 0 1 2 3 0 1 2 3 4 6 10 15 20 25 1/4" HEX SHAFT
<b>AUTOMOTIVE RATCHETING</b>	<b>BIT LOAD</b> 1 2 3 2 4 6 10 15 20 25 27 30 1/4" HEX SHAFT
<b>15:1 RV/MH</b>	<b>BIT LOAD</b> 3/16 5/32 0 1 2 3 1 2 4 6 10 15 20 25 1/4" HEX SHAFT
<b>15:1 HEX</b>	<b>BIT LOAD</b> 3/32 7/64 1/8 9/64 5/32 3/16 7/32 1/4 2 3 4 5 5.5 6 1/4" HEX SHAFT
<b>ELEVATOR 15:1</b>	<b>BIT LOAD</b> 0 1 2 3 6 8 10 12 4 6 10 15 20 25 1/4" HEX SHAFT
<b>ELECTRONIC</b>	<b>BIT LOAD</b> 0 1 2 3 6 8 10 12 1 2 4 6 10 15 1/4" HEX SHAFT
<b>AUTOMOTIVE 14:1</b>	<b>BIT LOAD</b> 1 2 9 10 15 20 25 27 30 40 5.5 VALVE STEM SOCKET ADAPTER 1/4" HEX SHAFT
<b>compact</b> RATCHETING	<b>BIT LOAD</b> 1 2 1 2 4 6 1/4" HEX SHAFT



SCREWDRIVERS						
PART #	UPC	DESCRIPTION	Std	Mstr	Unit	
	D151	10282 ORIGINAL 15 in One - Carded		1	10	Ea
	D151X	84148 ORIGINAL 15 in One - <b>Bulk/Labeled</b>		1	10	Ea
	D151TP	10266 TAMPERPROOF – Carded		1	10	Ea
	D151TPX	84149 TAMPERPROOF - <b>Bulk/Labeled</b>		1	10	Ea
	D151TP2	84145 TAMPERPROOF2 – Carded		1	10	Ea
	D151TP2X	84150 TAMPERPROOF2 – <b>Bulk/Labeled</b>		1	10	Ea
	D151HVAC	10267 HVAC – Carded		1	10	Ea
	D151HVACX	84151 HVAC – <b>Bulk/Labeled</b>		1	10	Ea
	D151HVACND	84152 HVAC W/ 5/16" MINI NUT DRIVER – Carded		1	10	Ea
	D151HVACNDX	84153 HVAC WITH 5/16" MINI NUT DRIVER – <b>Bulk/Labeled</b>		1	10	Ea
	D151SL44	84154 SHAFTLOK – Carded		1	10	Ea
	D151SL44X	84155 SHAFTLOK – <b>Bulk/Labeled</b>		1	10	Ea
	D151SS	10265 STAINLESS STEEL – Carded		1	10	Ea
	D151SSX	84156 STAINLESS STEEL - <b>Bulk/Labeled</b>		1	10	Ea
	D151HX	84157 HEX – Carded		1	10	Ea
	D151HXX	84158 HEX – <b>Bulk/Labeled</b>		1	10	Ea
	D6PDRIVER	84209 Pocket Driver -		1	10	Ea




**SCREWDRIVERS**


PART #	UPC	DESCRIPTION	Std	Mstr	Unit
 <b>D141AUTO</b>	84159	AUTOMOTIVE – Carded 	1	10	Ea
 <b>D141AUTOX</b>	84160	AUTOMOTIVE – <b>Bulk/Labeled</b>	1	10	Ea
 <b>D151YWRDPLR</b>	84161	PL ROBERTSON (SQUARE) – Carded 	1	10	Ea
 <b>D151YWRDPLRX</b>	84162	PL ROBERTSON (SQUARE) – <b>Bulk/Labeled</b>	1	10	Ea
 <b>D151RV</b>	84163	RECREATIONAL VEHICLE – Carded 	1	10	Ea
 <b>D151RVX</b>	84164	RECREATIONAL VEHICLE – <b>Bulk/Labeled</b>	1	10	Ea
 <b>D151ELECCHRD</b>	84165	ELECTRONIC – Carded 	1	10	Ea
 <b>D151ELECCHRD X</b>	84166	ELECTRONIC – <b>Bulk/Labeled</b>	1	10	Ea
 <b>D151ELEVCHOR</b>	84167	ELEVATOR – Carded 	1	10	Ea
 <b>D151ELEVCHOR X</b>	84168	ELEVATOR – <b>Bulk/Labeled</b>	1	10	Ea
 <b>D171005X</b>	84169	COMPACT STUBBY - <b>Bulk/Labeled</b> 	1	10	Ea
 <b>D171BKRDX</b>	84170	COMPACT STANDARD – <b>Bulk/Labeled</b> 	1	10	Ea
 <b>D171BKRDRX</b>	84171	COMPACT RATCHETING – <b>Bulk/Labeled</b> 	1	10	Ea
 <b>D181MKX</b>	84172	MEGALOK – <b>Bulk/Labeled</b> 	1	10	Ea
 <b>D211R1C36RD</b>	84173	AUTOMOTIVE RATCHETING – Carded 	1	10	Ea
 <b>D211R1C36RDX</b>	84174	AUTOMOTIVE RATCHETING – <b>Bulk/Labeled</b>	1	10	Ea
 <b>D131R</b>	81251	RATCHETING – Carded 	1	10	Ea
 <b>D131RX</b>	84175	RATCHETING - <b>Bulk/Labeled</b>	1	10	Ea



### NICKEL PLATED REPLACEMENT BITS – Two Bits per Card


PART #	UPC	DESCRIPTION		Std	Mstr	Unit
<b>NBP03C</b>	81953	#0 - #3 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>NBP12C</b>	81954	#1 - #2 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>NBS03C</b>	81955	#0 - #3 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>NBS12C</b>	81956	#1 - #2 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>NBSL46C</b>	81957	#4 - #6 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>NBT1015C</b>	81951	T10 - T15 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>NBT2025C</b>	81952	T20 - T25 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>RBVC</b>	81958	Carded Replacement Bits for Multi Bit Drivers Valve Stem		1	5	Ea
<b>SA14C</b>	81959	Carded Replacement Bits for Multi Bit Drivers 1/4" Socket		1	5	Ea

### TAMPER PROOF REPLACEMENT BITS – Two Bits per Card

PART #	UPC	DESCRIPTION		Std	Mstr	Unit
<b>RHP18C</b>	81963	Hex Pin 1/8 - 9/64 Carded Replacement Bits for Multi Bit Driver		1	5	Ea
<b>RHP532C</b>	81964	Hex Pin 5/32 - 3/16 Carded Replacement Bits for Multi Bit Drive		1	5	Ea
<b>RSP12C</b>	81966	Spanner #10 - #12 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>RSP68C</b>	81965	Spanner #6 - #8 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>RTP15C</b>	81960	Star Pin T10 - T15 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>RTP20C</b>	81961	Star Pin T20 - T25 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea
<b>RTP27C</b>	81962	Star Pin T27 - T30 Carded Replacement Bits for Multi Bit Drivers		1	5	Ea




**TAMPER PROOF 2 REPLACEMENT BITS – Two Bits per Card**

PART #	UPC	DESCRIPTION		Std	Mstr	Unit
DTPDT1015	84176	Torx-Plus Tamperproof2 Bit 10-15		1	5	Ea
DTPDT2025	84177	Torx-Plus Tamperproof2 Bit 20-25		1	5	Ea
DTPDT2730	84178	Torx-Plus Tamperproof2 Bit 27-30		1	5	Ea
DTSDT46	84179	Torq-Set Tamperproof 2 Bit 4-6		1	5	Ea
DTSDT810	84180	Torq-Set Tamperproof 2 Bit 8-10		1	5	Ea
DTWDT23	84181	Tri-Wing Tamperproof2 Bit 2-3		1	5	Ea
DTWDT45	84182	Tri-Wing Tamperproof2 Bit 4-5		1	5	Ea




**STANDARD DOUBLE END STEEL BITS – Two Bits per Card**

PART #	UPC	DESCRIPTION		Std	Mstr	Unit
DFD24	84183	Flat (Slot) Bit 2-4		1	5	Ea
DFD35	84184	Flat (Slot) Bit 3-5		1	5	Ea
DPD03	84185	Phillips Bit 0-3		1	5	Ea
DPD12	84186	Phillips Bit 1-2		1	5	Ea
DSD03	84187	Square Bit 0-3		1	5	Ea
DSD12	84188	Square Bit 1-2		1	5	Ea




**DOUBLE END - SHAFTLOC STEEL BITS – Two Bits per Card**

PART #	UPC	DESCRIPTION 	Std	Mstr	Unit
DF4D46	84196	Flat (Slot) ShaftLok Bit 4-6	1	5	Ea
DP4D03	84197	Phillips ShaftLok Bit 0-3	1	5	Ea
DP4D12	84198	Phillips ShaftLok Bit 1-2	1	5	Ea
DS4D03	84199	Square (Robertson) ShaftLok Bit 0-3	1	5	Ea
DS4D12	84200	Square (Robertson) ShaftLok Bit 1-2	1	5	Ea
DT4D1015	84201	Star (Torx) ShaftLok Bit 10-15	1	5	Ea
DT4D2025	84202	Star (Torx) ShaftLok Bit 20-25	1	5	Ea







**SHAFTLOC EXTENTIONS – One Extension per Card**

PART #	UPC	DESCRIPTION 	Std	Mstr	Unit
D6EXTSL6C	84203	ShaftLok 6" Extension - Black Oxide - Carded	1	5	Ea
D6EXTSL10C	84204	ShaftLok 10" Extension - Black Oxide - Carded	1	5	Ea



**AUTHENTIC DOUBLE END PL ROBERTSON BITS - Two Bits per Card**

PART #	UPC	DESCRIPTION	Std	Mstr	Unit
SD00PLRY	84205	Square Bit Yellow Double End 0-0 	1	5	Ea
SD11PLRG	84206	Square Bit Green Double End 1-1 	1	5	Ea
SD22PLRR	84207	Square Bit Red Double End 2-2 	1	5	Ea
SD33PLRB	84208	Square Bit Black Double End 3-3 	1	5	Ea