

# Low Voltage & Communication Fasteners

Eaton offers a wide variety of B-Line series cable management solutions that are ideal for data centers and light-duty commercial, low voltage telecommunication and network cable organization.

- Com Dangle Cable Management Solution - ideal for ceiling wire applications, and easily integrates into the ceiling grid with only tie off wires where jurisdiction requires.
- J-Hook Cable Management - available as a single cable retainers or as a single or double sided, multi-tiered j-hook. These hooks are ideal to support all category 5/5e/6, fiber optic, inner duct, and low voltage cable.
- J-Hook Color ID Clips - ideal alternative to long-lead time custom painted j-hook cable managers, Eaton's B-Line series j-hooks combined with j-hook color ID clips allow installers and inspectors to easily verify that cables are running in their correct, designated pathways.
- Bridle Rings - convenient easy to use, with the cable bearing surface of a hook, supports a variety of mounting and hanging applications.



Material:	Type	Thickness	Specifications
	Steel Bar	3/8" (9.5mm) - 7 Gauge (4.5mm)	ASTM A36
	Steel Strip	10 Gauge (3.4mm) - 12 Gauge (2.6mm)	ASTM A569
	Aluminum		6061-T6 & 6063-T6

# Low Voltage & Communication Fasteners

Low voltage & communication fasteners

## Cable Hooks

- Supports all category 5/5e/6, fiber optic, innerduct, and low voltage cabling requirements
- Finish is Pre-Galvanized Steel
- Static Load Capacity: 30 lbs. (13.6kg)
- Exclusive Qwik-Latch™ cable retainers provide secure containment of cables and are included in each box of cable hooks
- Quick open and close design for adding and removing cable runs
- Plenum-rated Qwik-Latch is more economical than plenum-rated cable ties
- Box Quantity: BCH12, BCH21, and BCH32 - 50 • BCH64 - 25



Patent #5961081

Part Number	Hook Size		Capacity	Wt. Per 100	
	In.	(mm)		Lbs.	(kg)
<b>BCH12</b>	¾"	(19.0)	16 4-Pair UTP	7.0	(3.2)
<b>BCH21</b>	1½"	(38.3)	50 4-Pair UTP	15.4	(7.0)
<b>BCH32</b>	2"	(50.8)	80 4-Pair UTP	20.6	(9.3)
<b>BCH64</b>	4"	(101.6)	300 4-Pair UTP	56.0	(25.4)



## Painted Cable Hooks

- Powder coated cable hooks are available in a range of colors to help meet your cable identification requirements.
- Standard riveted assemblies are available with painted cable hooks.
- Part numbers can be made by adding the paint color suffix after the cable hook part number
- Minimum order quantity 500 pieces.
- Standard lead time is 5-10 working days.

### Colors

- |                     |                    |
|---------------------|--------------------|
| Bright White - BW   | Green - GR         |
| Brown - BR          | Orange - OR        |
| Computer White - CW | Regal Red - RR     |
| Equipment Blue - BL | Safety Yellow - YL |
| Flat Black - FB     | Telcom Gray - TG   |



Part # Example:

Painted Cable Hook Part Number - BCH32BW  
Painted Cable Hook Assembly - BCH32BW-U24


# Low Voltage & Communication Fasteners

## X-Hook Low Friction Cable Hooks

- Xylan<sup>†</sup> coating provides smooth frictionless surface for cable pulling
- Great for use in corners, drop-outs or any direction change in the cable run
- X-Hook has lower coefficient of friction than Teflon<sup>†</sup>
- Includes Quik-Latch cable retainer
- Box Quantity: BCH21X and BCH32X - 50  
BCH64X - 25

Part Number	Hook Size		Capacity	Wt. Per 100	
	In.	(mm)		Lbs.	(kg)
BCH21X	1 $\frac{5}{16}$ "	(33.3)	50 4-Pair UTP	15.4	(7.0)
BCH32X	2"	(50.8)	80 4-Pair UTP	20.6	(9.3)
	4"	(101.6)	300 4-Pair UTP	56.0	(25.4)

Available with most fastener assemblies. See the following pages.




New Xylan coating reduces cable friction. Ideal for pulling cable.

Low voltage & communication fasteners



Cable rollers are too expensive and require installation and removal.





<sup>†</sup> Marks shown are property of respective owners.

### Cable To Beam Fasteners

- Permits fast and easy installation on beam flanges
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Simply installed with a hammer
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12, BCH21, and BCH32 - 50 • BCH64 - 25

Part Number	Hook Size		Flange Thickness		Wt. Per 100	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
<b>BCH12-U-2-4</b>	¾"	(19.0)	⅛" to ¼"	(3.2 to 6.3)	35.0	(15.9)
<b>BCH12-U-5-8</b>	¾"	(19.0)	⅝" to ½"	(7.9 to 12.7)	36.0	(16.3)
<b>BCH12-U-9-12</b>	¾"	(19.0)	⅞" to ¾"	(14.3to 19.0)	37.0	(16.8)
<b>BCH21-U-2-4 *</b>	1⅝"	(33.3)	⅛" to ¼"	(3.2 to 6.3)	40.4	(18.3)
<b>BCH21-U-5-8 *</b>	1⅝"	(33.3)	⅝" to ½"	(7.9 to 12.7)	40.2	(18.2)
<b>BCH21-U-9-12 *</b>	1⅝"	(33.3)	⅞" to ¾"	(14.3to 19.0)	42.6	(19.3)
<b>BCH32-U-2-4 *</b>	2"	(50.8)	⅛" to ¼"	(3.2 to 6.3)	44.6	(20.2)
<b>BCH32-U-5-8 *</b>	2"	(50.8)	⅝" to ½"	(7.9 to 12.7)	46.4	(21.0)
<b>BCH32-U-9-12 *</b>	2"	(50.8)	⅞" to ¾"	(14.3to 19.0)	46.8	(21.2)
<b>BCH64-U-2-4 *</b>	4"	(101.6)	⅛" to ¼"	(3.2 to 6.3)	98.0	(44.4)
<b>BCH64-U-5-8 *</b>	4"	(101.6)	⅝" to ½"	(7.9 to 12.7)	96.0	(43.5)
<b>BCH64-U-9-12 *</b>	4"	(101.6)	⅞" to ¾"	(14.3to 19.0)	97.2	(44.1)

\* For Xylan® coating, add "X" after cable hook part number. Ex: BCH32X-U-5-8



Allows 360° Rotation





### Cable To Beam Fasteners

- Permits fast and easy installation on beam flanges
- Qwik-Latch cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Simply installed with a hammer
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12 and BCH21 - 50 • BCH32 - 25

Part Number	Hook Size		Flange Thickness		Wt. Per 100	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
<b>BCH12-E-2-4</b>	¾"	(19.0)	⅛" to ¼"	(3.2 to 6.3)	11.0	(5.0)
<b>BCH12-E-5-8</b>	¾"	(19.0)	⅝" to ½"	(7.9 to 12.7)	11.0	(5.0)
<b>BCH12-E-9-12</b>	¾"	(19.0)	⅞" to ¾"	(14.3to 19.0)	12.0	(5.4)
<b>BCH21-E-2-4 *</b>	1⅝"	(33.3)	⅛" to ¼"	(3.2 to 6.3)	18.4	(8.3)
<b>BCH21-E-5-8 *</b>	1⅝"	(33.3)	⅝" to ½"	(7.9 to 12.7)	22.6	(10.2)
<b>BCH21-E-9-12 *</b>	1⅝"	(33.3)	⅞" to ¾"	(14.3to 19.0)	19.8	(9.0)
<b>BCH32-E-2-4 *</b>	2"	(50.8)	⅛" to ¼"	(3.2 to 6.3)	23.8	(10.8)
<b>BCH32-E-5-8 *</b>	2"	(50.8)	⅝" to ½"	(7.9 to 12.7)	24.4	(11.0)
<b>BCH32-E-9-12 *</b>	2"	(50.8)	⅞" to ¾"	(14.3to 19.0)	24.6	(11.1)

\* For Xylan® coating, add "X" after cable hook part number. Ex: BCH32X-E-5-8



® All trademarks are property of their respective owners.


### Cable To Beam Fasteners

- 360° rotation allows cable to run in any direction
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Simply installed with a screwdriver
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size		Flange Thickness	Wt. Per 100	
	In.	(mm)		Lbs.	(kg)
BCH12-C2	¾"	(19.0)	Thru ½" (13mm)	17.4	(7.9)
BCH21-C2 *	1⅝"	(33.3)	Thru ½" (13mm)	39.8	(18.0)
BCH32-C2 *	2"	(50.8)	Thru ½" (13mm)	45.0	(20.4)
BCH64-C2 *	4"	(101.6)	Thru ½" (13mm)	95.6	(43.3)

\* For Xylan®† coating, add "X" after cable hook part number. Ex: BCH32X-C2




### Cable To Beam Fasteners

- 360° rotation allows cable to run in any direction
- Qwik-Latch cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Simply installed with a screwdriver
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size		Flange Thickness		Wt. Per 100	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
BCH12-C442	¾"	(19.0)	⅛" - ⅝"	(3 - 16)	23.5	(10.6)
BCH21-C442 *	1⅝"	(33.3)	⅛" - ⅝"	(3 - 16)	45.8	(20.8)
BCH32-C442 *	2"	(50.8)	⅛" - ⅝"	(3 - 16)	51.6	(23.4)
BCH64-C442 *	4"	(101.6)	⅛" - ⅝"	(3 - 16)	102.4	(46.6)


\* For Xylan®† coating, add "X" after cable hook part number. Ex: BCH32X-C442



† All trademarks are property of their respective owners.


### Cable To Beam Fasteners

- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Simply installed with a screwdriver
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25




Part Number	Hook Size		Flange Thickness	Wt. Per 100	
	In.	(mm)		Lbs.	(kg)
BCH12-C1	3/4"	(19.0)	Thru 1/2" (13mm)	12.3	(5.6)
BCH21-C1 *	1 5/16"	(33.3)	Thru 1/2" (13mm)	20.7	(9.4)
BCH32-C1 *	2"	(50.8)	Thru 1/2" (13mm)	25.9	(11.7)
BCH64-C1 *	4"	(101.6)	Thru 1/2" (13mm)	61.3	(27.8)

\* For Xylan®† coating, add "X" after cable hook part number. Ex: BCH32X-C1




### Cable To Beam Fasteners

- Qwik-Latch cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Simply installed with a screwdriver
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size		Flange Thickness		Wt. Per 100	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
BCH12-C442A	3/4"	(19.0)	1/8" - 5/8"	(3 - 16)	18.4	(8.3)
BCH21-C442A *	1 5/16"	(33.3)	1/8" - 5/8"	(3 - 16)	26.8	(12.1)
BCH32-C442A *	2"	(50.8)	1/8" - 5/8"	(3 - 16)	32.0	(14.5)
BCH64-C442A *	4"	(101.6)	1/8" - 5/8"	(3 - 16)	67.4	(30.6)

\* For Xylan®† coating, add "X" after cable hook part number. Ex: BCH32X-C442A



®† All trademarks are property of their respective owners.



### Cable To Flange Fasteners

- Supports cable from vertical flanges
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Simply installed with a hammer
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size		Flange Thickness		Wt. Per 100	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
BCH12-F3	3/4"	(19.0)	1/16" - 1/4"	(1.6 - 6.3)	13.0	(5.9)
BCH21-F3 *	1 5/16"	(33.3)	1/16" - 1/4"	(1.6 - 6.3)	21.0	(9.5)
BCH32-F3 *	2"	(50.8)	1/16" - 1/4"	(1.6 - 6.3)	26.0	(11.8)
BCH64-F3 *	4"	(101.6)	1/16" - 1/4"	(1.6 - 6.3)	62.4	(28.3)

\* For Xylan® coating, add "X" after cable hook part number. Ex: BCH32X-F3





### Cable To Flange Fasteners

- Supports cable from angled flanges
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Simply installed with a hammer
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size		Flange Thickness		Wt. Per 100	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
BCH12-F4	3/4"	(19.0)	1/16" - 1/4"	(1.6 - 6.3)	13.0	(5.9)
BCH21-F4 *	1 5/16"	(33.3)	1/16" - 1/4"	(1.6 - 6.3)	21.0	(9.5)
BCH32-F4 *	2"	(50.8)	1/16" - 1/4"	(1.6 - 6.3)	25.8	(11.7)
BCH64-F4 *	4"	(101.6)	1/16" - 1/4"	(1.6 - 6.3)	62.4	(28.3)

\* For Xylan® coating, add "X" after cable hook part number. Ex: BCH32X-F4



Patent #5961081

®† All trademarks are property of their respective owners.



### Cable To Rod Fasteners

- Supports cable from #12 wire thru 3/8" threaded rod
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Static Load Capacity: 25 lbs. (11.3kg)
- W2 series attaches to #12 wire thru 1/4" plain or threaded rod
- W6 series attaches to 3/8" plain or threaded rod
- Box Quantity - 50



Part Number	Hook Size		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
BCH12-W2	3/4"	(19.0)	10.0	(4.5)
BCH21-W2 *	1 5/16"	(33.3)	17.6	(8.0)
BCH32-W2 *	2"	(50.8)	23.4	(10.6)
BCH12-W6	3/4"	(19.0)	10.0	(4.5)
BCH21-W6 *	1 5/16"	(33.3)	17.8	(8.1)
BCH32-W6 *	2"	(50.8)	23.6	(10.7)

\* For Xylan®† coating, add "X" after cable hook part number. Ex: BCH32X-W6





### Cable To T-Bar Fasteners

- Supports cable above ceiling grid
- Qwik-Latch cable retainers included (not shown on drawings)
- Designed to accept cable ties
- 360° rotation allows cable to run in any direction
- Provides compliance with 1997 EIA/TIA standard 569-A
- Permits dropwire attachment if required
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity - 50



Part Number	Hook Size		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
BCH12-A28	3/4"	(19.0)	23.0	(10.4)
BCH21-A28 *	1 5/16"	(33.3)	30.6	(13.9)
BCH32-A28 *	2"	(50.8)	36.8	(16.7)

\* For Xylan®† coating, add "X" after cable hook part number. Ex: BCH32X-A28





®† All trademarks are property of their respective owners.

### Cable To Floor Support Fasteners

- Supports cable from computer floor post
- Organizes cable off the floor for a neat installation
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Static Load Capacity: 30 lbs. (13.6kg)
- Finish: Pre-galvanized
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size - Floor Post Size	Wt. Per 100	
		Lbs.	(kg)
BCH12-L1410	¾" - 1" O.D.	13.4	(6.1)
BCH21-L1410	1½/16" - 1" O.D.	22.8	(10.3)
BCH32-L1410	2" - 1" O.D.	28.4	(12.9)
BCH64-L1410	4" - 1" O.D.	64.0	(29.0)





### Cable To Floor Support Fasteners

- Supports cable from square computer floor post
- Organizes cable off the floor for a neat installation
- Qwik-Latch cable retainers included (not shown on drawings)
- Static Load Capacity: 30 lbs. (13.6kg)
- Finish: Pre-galvanized
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size - Floor Post Size	Wt. Per 100	
		Lbs.	(kg)
BCH12-G-8-12	¾" - 1" Square	13.4	(6.1)
BCH21-G-8-12	1½/16" - 1" Square	22.8	(10.3)
BCH32-G-8-12	2" - 1" Square	28.4	(12.9)
BCH64-G-8-12	4" - 1" Square	64.0	(29.0)



# Low Voltage & Communication Fasteners

Low voltage & communication fasteners

## Cable To ATR Fasteners



- .505" (12.8mm) diameter hole designed to support cable from 3/8" or 1/2" threaded rod
- Allows back-to-back and multi-tier installations
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH21 and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
<b>BCH21-AB *</b>	1 5/16"	(33.3)	34.2	(15.5)
<b>BCH32-AB *</b>	2"	(50.8)	40.0	(18.1)
<b>BCH64-AB *</b>	4"	(101.6)	91.2	(41.3)

\* For Xylan®+ coating, add "X" after cable hook part number.  
Ex: BCH32X-AB

Note: Part numbers listed are for galvanized hooks - Add "SS4" for Stainless Steel.



## Angle Bracket Cable Fasteners



- Designed for direct attachment to structures
- Supports cable from 1/4" threaded rod
- .265" (6.7mm) diameter hole accepts anchors, screws or common nails
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity: BCH12, BCH21, and BCH32 - 50  
BCH64 - 25



Part Number	Hook Size		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
<b>BCH12-RB</b>	3/4"	(19.0)	29.0	(13.2)
<b>BCH21-RB *</b>	1 5/16"	(33.3)	34.4	(15.6)
<b>BCH32-RB *</b>	2"	(50.8)	39.4	(17.9)
<b>*</b>	4"	(101.6)	91.2	(41.3)

\* For Xylan®+ coating, add "X" after cable hook part number.  
Ex: BCH32X-RB

Note: Part numbers listed are for galvanized hooks - Add "SS4" for Stainless Steel.




®+ All trademarks are property of their respective owners.

# Low Voltage & Communication Fasteners

## Single-Sided Multi-Tier Cable Fasteners

- Factory assembled multi-tier fasteners increase installation flexibility
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Available in two-tier through six-tier assemblies
- Unique design prevents hooks and assembly from rotating when pulling cable
- All support bars furnished in 6063-T6 aluminum
- Static Load Capacity: 30 lbs. (13.6kg)
- Box Quantity - 10




Low voltage & communication fasteners

Part Number	Hook Size		Overall Height		Wt. Per 100	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
BCH21-2S	1 <sup>5</sup> / <sub>16</sub> "	(33.3)	11"	(279)	65.0	(29.5)
BCH32-2S	2"	(50.8)	12 <sup>3</sup> / <sub>4</sub> "	(324)	78.0	(35.4)
BCH64-2S	4"	(101.6)	19 <sup>5</sup> / <sub>16</sub> "	(490)	94.0	(42.6)
BCH21-3S	1 <sup>5</sup> / <sub>16</sub> "	(33.3)	14 <sup>3</sup> / <sub>4</sub> "	(374)	99.0	(44.9)
BCH32-3S	2"	(50.8)	17 <sup>1</sup> / <sub>2</sub> "	(444)	122.0	(55.3)
BCH64-3S	4"	(101.6)	28 <sup>1</sup> / <sub>16</sub> "	(713)	148.0	(67.1)
BCH21-4S	1 <sup>5</sup> / <sub>16</sub> "	(33.3)	18 <sup>1</sup> / <sub>2</sub> "	(470)	133.0	(60.3)
BCH32-4S	2"	(50.8)	21 <sup>3</sup> / <sub>4</sub> "	(552)	166.0	(75.3)
BCH21-5S	1 <sup>5</sup> / <sub>16</sub> "	(33.3)	21 <sup>3</sup> / <sub>4</sub> "	(552)	167.0	(75.7)
BCH32-5S	2"	(50.8)	27"	(686)	182.0	(82.5)
BCH21-6S	1 <sup>5</sup> / <sub>16</sub> "	(33.3)	26"	(660)	201.0	(91.2)
BCH32-6S	2"	(50.8)	31 <sup>3</sup> / <sub>4</sub> "	(806)	222.0	(100.7)

\_\_ = Color (FB = Flat Black, EW = Eaton White)

\* Suggested use only. Configurations may vary based on customer or application requirements.




# Low Voltage & Communication Fasteners


Low voltage & communication fasteners

## Double-Sided Multi-Tier Cable Fasteners

- Factory assembled multi-tier fasteners increase installation flexibility
- Unique design prevents hooks and assembly from rotating when pulling cable
- All support bars furnished in 6063-T6 aluminum
- Shown (at right) with optional BCHK2 kit
- Qwik-Latch™ cable retainers included (not shown on drawings)
- Designed to accept cable ties
- Static Load Capacity: (per hook) 30 lbs. (13.6kg)
- Box Quantity: BCH21-1D and BCH32-1D - 20  
BCH64-1D and All 2D Fasteners - 10



Part Number	Hook Size		Overall Height		Wt. Per 100	
	In.	(mm)	In.	(mm)	Lbs.	(kg)
BCH21-1D	1 <sup>5</sup> / <sub>16</sub> "	(33.3)	5 <sup>1</sup> / <sub>2</sub> "	(140)	46.0	(20.8)
BCH32-1D	2"	(50.8)	6 <sup>3</sup> / <sub>16</sub> "	(157)	63.0	(28.6)
BCH64-1D	4"	(101.6)	9"	(228)	144.0	(65.3)
BCH21-2D	1 <sup>5</sup> / <sub>16</sub> "	(33.3)	9 <sup>1</sup> / <sub>4</sub> "	(234)	101.0	(45.8)
BCH32-2D	2"	(50.8)	11"	(279)	112.0	(50.8)
BCH64-2D	4"	(101.6)	18 <sup>1</sup> / <sub>4</sub> "	(463)	287.0	(130.2)




Patent #5961081

Note: Part numbers listed above are for galvanized hooks - Add "SS4" for Stainless Steel or add "H" for Zinc-Plated Spring Steel for heavy-duty applications.

## Multi-Tier Attachment Kits


- Kits permit secure attachment of single-tier and multi-tier fasteners.
- BCHK1 includes:
  - 1 ea. beam clamp (B444-1/4)
  - 1 ea. 1/4"-20 x 1/2" hex head cap screw
- BCHK2 includes:
  - 1 ea. angle bracket (with .320"Ø and .390"Ø holes)
  - 1 ea. 5/16"-18 x 3/4" hex head cap screw
  - 1 ea. 5/16"-18 hex nut
- BCHK3 includes:
  - 1 ea. BCHK1 Kit
  - 1 ea. BCHK2 Kit
- Box Quantity - 10



**BCHK2**  
Angle Bracket



**BCHK1**  
Beam Clamp



**BCHK3**  
Beam Clamp with  
Angle Bracket  
(Swivels 360°)

Part Number	Flange Thickness		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
BCHK1	thru 5/8"	(thru 15.9)	27.0	(12.2)
BCHK2	—	—	43.0	(19.5)
BCHK3	thru 5/8"	(thru 15.9)	67.0	(30.4)

# Low Voltage & Communication Fasteners

## J-Hook Color ID Clip

- Color-coded clips allow for content designation without inventorying various colored hardware.
- Easy to designate pathways to prevent crossover.
- Order separately and field install.
- Can be snapped on J-Hook after it has been installed.
- Manufactured from Underwriters Laboratories (UL) Listed material for plenum spaces.
- Suitable for ¾", 15/16", 2", and 4" J-Hook sizes.
- Available in six (6) colors: Blue (BL), White (WH), Gray (GY), Orange (OR), Red (RD), and Yellow (YW).



Part # Example: Blue Colored ID Clip Part Number BCHID-BL12 - blue clip for BCH12 J-Hook  
See page 212 for cable hooks.

Low voltage & communication fasteners

## COM Dangle System Load Table – Number of Cables Allowed

Part Number	Color	Diameter In. (mm)	Cat5e	Cat6	Cat6a
<b>BLCD8</b>	Neutral	2.5" (63mm)	110	75	50
<b>BLCD8RD</b>	Red	2.5" (63mm)	110	75	50
<b>BLCD8BL</b>	Blue	2.5" (63mm)	110	75	50
<b>BLCD12</b>	Neutral	4" (102mm)	220	150	115
<b>BLCD12RD</b>	Red	4" (102mm)	220	150	115
<b>BLCD12BL</b>	Blue	4" (102mm)	220	150	115

\*Contact factory for other color options

## COM Dangle™ Cable Support System

The COM Dangle system is an innovative, cost-efficient solution alternative to J-Hooks to help support cables in a data center environment. The system is ideal for ceiling wire applications, and can easily integrate to the ceiling grid with only tie-off wire where jurisdiction requires.


### Features

- Made from advanced polymer
- UL listed, Plenum rated and RoHS compliant
- Corrosion and chemical resistant
- High strength-to-weight ratio
- Abrasion and impact resistance over a wide range of temperatures
- Installs easily with minimal steps

### COM Dangle Standards

- Maximum 5 foot space between supports
- 20 lb. maximum weight
- 40% max fill based on TIA 569-B


®† All trademarks are property of their respective owners.





# Low Voltage & Communication Fasteners

## Cable Fasteners


- Supports cable ties up to 3/32" (7.1mm) wide from flanges 1/16" (1.6mm) to 3/4" (19.0mm)
- Designed for securing communications cables
- 8" (203mm) cable tie included
- Simply installed with a hammer
- Finish: Zinc Phosphate
- Box Quantity - 100



BE-\_\_-CT2





BF\_\_-CT2



Part Number	Description		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
BE-2-4-CT2	1/8" to 1/4"	(3.2 to 6.3)	4.4	(2.0)
BE-5-8-CT2	5/16" to 1/2"	(7.9 to 12.7)	4.8	(2.2)
BE-9-12-CT2	5/16" to 1/2"	(7.9 to 12.7)	5.4	(2.4)
BF1-CT2	1/16" to 5/32"	(1.6 to 3.9)	3.6	(1.6)
BF2-CT2	5/32" to 1/4"	(3.9 to 6.3)	3.6	(1.6)

## Cable Fasteners

- Supports cable ties up to 3/32" (7.1mm) wide from drop wires
- Designed for securing communications cables
- 8" (203mm) cable tie included
- Finish: Zinc Phosphate
- Box Quantity - 100




Part Number	Description	Wt. Per 100	
		Lbs.	(kg)
BW2-CT2	#12 Wire thru 1/4" Plain Rod"	3.9	(1.7)
BW6-CT2	3/8" Plain or Threaded Rod"	4.5	(2.0)

Low voltage & communication fasteners


# Low Voltage & Communication Fasteners

## Bridle Ring Saddles


- The convenience of a bridle ring with the cable-bearing surface of a hook
- 2" (51mm) saddle is available separately
- Can be easily attached before or after cable installation
- Box Quantity: BRS-32A and BRS-32 - 50  
BRS 64A - 25



BRS-32A




BRS-32



BRS-64A


Part Number	Thread Size x Description	Wt. Per 100	
		Lbs.	(kg)
BRS-32A	1/4"-20 x 7/8" 2" Ring Assembly	13.0	(5.89)
BRS-64A	1/4"-20 x 1" 4" Ring Assembly	30.0	(13.61)
BRS-32	2" Saddle Only	3.0	(1.36)




Low voltage & communication fasteners

## Threaded Bridle Rings

- Supports low voltage communication cables from wood beams
- Ultimate Load Capacity: 50 lbs. (22.7kg)
- Finish: Zinc Plated
- Box Quantity - 100




Part Number	Ring Size		Thread Size/Length	Wt. Per 100	
	In.	(mm)		Lbs.	(kg)
BR-16-3W	1"	(25.4)	3/16" x 9/16"	2.6	(1.18)
BR-24-4W	1 1/2"	(38.1)	1/4" x 27/32"	7.1	(3.22)
BR-32-4W	2"	(50.8)	1/4" x 7/8"	10.9	(4.94)



## Bridle Ring/Beam Fastener Assembly

- Supports low voltage communication cables from beam flanges 1/8" (3.2mm) to 3/4" (19.0mm) thick
- Pre-assembled with 2" (51mm) bridle ring
- Reduces installation time
- Static Load Capacity: 15 lbs. (6.8kg)
- Box Quantity - 50

Part Number	Flange Thickness		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
BR-32-4T-U-2-4	1/8" to 1/4"	(3.2 to 6.3)	14.6	(6.6)
BR-32-4T-U-5-8	5/16" to 1/2"	(7.9 to 12.7)	15.2	(6.9)
BR-32-4T-U-9-12	9/16" to 3/4"	(14.3 to 19.0)	16.6	(7.5)




# Low Voltage & Communication Fasteners

Low voltage & communication fasteners

## Bridle Ring/Rod & Wire Fastener Assy.

- Supports low voltage communication cables from drop wire
- Pre-assembled with 2" (51mm) bridle ring
- Reduces installation time
- Static Load Capacity: 15 lbs. (6.8kg)
- Box Quantity - 50


Part Number	Wire or Rod Size	Wt. Per 100	
		Lbs.	(kg)
<b>BR-32-4T-W2</b>	#12 Wire thru ¼" Plain or Threaded Rod	12.4	(5.6)



## Bridle Ring/T-Bar Fastener Assy.

- Supports low voltage communication cables from the T-Bar
- Pre-assembled with 2" (51mm) bridle ring
- Reduces installation time
- For positioning only - No Load Rating
- Box Quantity - 50


Part Number Saddle Only	Ring Size		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
<b>BR-32-4T-A6</b>	2"	(50.8)	11.6	(5.2)



## Bridle Ring/Beam Fastener Assy.

- Supports low voltage communication cables from beam flanges thru ½" (12.7mm) thick
- Pre-assembled with 2" (51mm) bridle ring
- Reduces installation time
- Static Load Capacity: 15 lbs. (6.8kg)
- Box Quantity - 50

Part Number Saddle Only	Ring Size		Wt. Per 100	
	In.	(mm)	Lbs.	(kg)
<b>BR-32-4T-C1</b>	2"	(50.8)	15.0	(6.8)



# Low Voltage & Communication Fasteners

## KwikWire Hanging System

- Flexible replacement for jack chain and all thread rod that will help reduce your installation time.
- Installs up to 50% faster - can quickly wrap around beams with no drilling required
- Simple height adjustments are made by releasing the clamp's adjustment pin - **no tools required**
- Aesthetic appeal - blends in with upper structural supports
- Compatible with many fastener, anchor, and hanger products reducing inventory & shipping costs
- Ideal for sloped ceiling applications - will support loads at up to a 60° angle from vertical
- 2 sku's cover a wide range of application requirements

## KwikWire Accessory Numbering System

Product Line	Assembly Configuration	Leg Termination	Leg Length	Wire Rope Diameter	Straight Length	Assembly or Kit
BK = KwikWire	Blank = Single Leg Y = 2 Legs 3 = 3 Legs	A = Angle Bracket w/Pin H = Hook L = Loop T = Toggle W = Fuse Cut B25 = Bolt w/ 1/4"-20 Thread B38 = Bolt w/ 3/8"-16 Thread BM6 = Bolt w/ M6 Thread BM8 = Bolt w/ M8 Thread BM10 = Bolt w/ M10 Thread	Blank = See Straight Length 18 = 18" Leg 30 = 30" Leg	063 = 1/16" 094 = 3/32"	Blank = Loop w/ Plastic Tube 18 = 18" 30 = 30" 40 = 40" 80 = 80" 120 = 120" 180 = 180" 240 = 240" 360 = 360"	Blank = Assembly Only K = Kit (Assembly & BKC100 Clamp)

## KwikWire™ Clamps

- KwikWire system replaces jack chain or ATR to support lighting, ductwork, cable tray, etc.
- Can be quickly installed around beams - No drilling required.
- Ideal for sloped ceilings - can hang objects at up to 60° angles.
- Simple height adjustments are made by releasing locking tab, no tools required.
- Spools of wire can be cut to length in field, reducing waste and up front planning.



Part Number	For Use With Wire Rope Diameters	Box Qty.
BKC100	1/16" & 3/32"	100
BKC200	1/8" & 3/16"	50

**\* Working loads shown are for hanging vertically. For suspending at 15°, 30°, 45° or 60° angles from vertical, use the following percentage of the working loads from the chart:**

**15° = 96%      45° = 70%**  
**30° = 86%      60° = 50%**

### KwikWire Clamp Working Loads\*

Clamp Part No.	Wire Rope Dia.	Lbs. Safety Factor 5
BKC100	1/16"	0-75
BKC100	3/32"	25-150
BKC200	3/32"	25-150
BKC200	1/8"	25-250
BKC200	3/16"	50-640

Read safety/installation instruction sheets in packages before use.

# Low Voltage & Communication Fasteners

Low voltage & communication fasteners

## KwikWire™ Wire Rope

- Finish: Uncoated Galvanized Wire



Part Number	Rope Dia. In. (mm)	Working Load Lbs. (kN)	Spool Qty. Ft. (m)
<b>BKW063</b> <sup>(1)</sup>	1/16" (1.59)	96 (0.43)	500 (152.4)
<b>BKW094</b> <sup>(1)</sup>	3/32" (2.36)	184 (0.82)	500 (152.4)
<b>BKW125</b> <sup>(1)</sup>	1/8" (3.17)	340 (1.51)	500 (152.4)
<b>BKW188</b> <sup>(2)</sup>	3/16" (4.77)	840 (3.73)	250 (76.2)

- <sup>(1)</sup> Wire Rope Construction Type 7 x 7
- <sup>(2)</sup> Wire Rope Construction Type 7 x 19



## KwikWire™ Cutter

- Used to cut wire rope.
- Never use cutter on energized circuits, wire, or cable.
- Box Quantity - 1

Part Number	Wt. Per 100 Lbs. (kg)
<b>BKCC</b>	1.0 (0.45)



## KwikPak™

- KwikPak include KwikWire clamps and a spool of wire rope
- KwikPaks are shipped in a specially designed dispenser box to ease field cutting of wire



Part Number	Kit Includes	Box Qty.
<b>BKP10063</b>	BKC100 (100 pcs.) 1/16" Diameter Wire Rope (500 ft.)	1
<b>BKP10094</b>	BKC100 (100 pcs.) 3/32" Diameter Wire Rope (500 ft.)	1
<b>BKP20125</b>	BKC200 (50 pcs.) 1/8" Diameter Wire Rope (500 ft.)	1
<b>BKP20188</b>	BKC200 (50 pcs.) 3/16" Diameter Wire Rope (250 ft.)	1

Read safety/installation instruction sheets in packages before use.

# Low Voltage & Communication Fasteners


## KwikWire™ Hanger

- KwikWire hanger combines the versatility of a bolt with an adjustable wire rope solution.
- Can be quickly installed in existing anchors or metal brackets with a nut.
- ARS, ARC, and ARW anchors are ideal for use with KwikWire Hangers.
- Ideal for supporting light fixtures, wire basket cable tray, HVAC ducts, and sign/banner supports.
- Allows for tool-less adjustment of wire rope.



Part Number	Thread Size	For Use With Wire Rope Diameters	Loading SF5	
			lbs.	(kg)
BKF100-4	1/4"-20	1/16"	45	(20.0)
		3/32"	90	(40.0)
BKF100-6	3/8"-16	1/8"	45	(20.0)
		3/16"	90	(40.0)

Low voltage & communication fasteners



## KwikWire Hanger Installation

1. Screw KwikWire Hanger into installed hanger support (ARS anchor pictured)
2. Push cable wire up through the bottom of KwikWire Hanger
3. Continue pushing through until 1/4" minimum is extending out the side of the KwikWire Hanger
4. To adjust up - pull or push more cable wire through KwikWire Hanger
5. To adjust down - push up on bottom of KwikWire Hanger and allow cable wire to feed down
6. When hanging the cable wire is complete, cut off any excess cable wire if desired

# Low Voltage & Communication Fasteners

## KwikWire™ Loop Termination

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
<b>BKL-063-40</b>	1/16"	(1.59)	40"	(1016)
<b>BKL-063-80</b>	1/16"	(1.59)	80"	(2032)
<b>BKL-063-120</b>	1/16"	(1.59)	120"	(3948)
<b>BKL-063-180</b>	1/16"	(1.59)	180"	(4572)
<b>BKL-063-240</b>	1/16"	(1.59)	240"	(6096)
<b>BKL-063-360</b>	1/16"	(1.59)	360"	(9144)
<b>BKL-094-40</b>	3/32"	(2.36)	40"	(1016)
<b>BKL-094-80</b>	3/32"	(2.36)	80"	(2032)
<b>BKL-094-120</b>	3/32"	(2.36)	120"	(3948)
<b>BKL-094-180</b>	3/32"	(2.36)	180"	(4572)
<b>BKL-094-240</b>	3/32"	(2.36)	240"	(6096)
<b>BKL-094-360</b>	3/32"	(2.36)	360"	(9144)




**Box Quantity - 20**  
5 bags containing 4 pieces per bag

## KwikWire™ Loop Termination Kits

- Available as a wire rope with loop termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360".

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
<b>BKL-063-40K</b>	1/16"	(1.59)	40"	(1016)
<b>BKL-063-80K</b>	1/16"	(1.59)	80"	(2032)
<b>BKL-063-120K</b>	1/16"	(1.59)	120"	(3948)
<b>BKL-063-180K</b>	1/16"	(1.59)	180"	(4572)
<b>BKL-063-240K</b>	1/16"	(1.59)	240"	(6096)
<b>BKL-063-360K</b>	1/16"	(1.59)	360"	(9144)
<b>BKL-094-40K</b>	3/32"	(2.36)	40"	(1016)
<b>BKL-094-80K</b>	3/32"	(2.36)	80"	(2032)
<b>BKL-094-120K</b>	3/32"	(2.36)	120"	(3948)
<b>BKL-094-180K</b>	3/32"	(2.36)	180"	(4572)
<b>BKL-094-240K</b>	3/32"	(2.36)	240"	(6096)
<b>BKL-094-360K</b>	3/32"	(2.36)	360"	(9144)



**Box Quantity - 20**  
5 bags containing 4 pieces per bag

Read safety/installation instruction sheets in packages before use.

# Low Voltage & Communication Fasteners

## KwikWire™ Single Style Hook Termination

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
BKH-094-40	3/32"	(2.36)	40"	(1016)
BKH-094-80	3/32"	(2.36)	80"	(2032)
BKH-094-120	3/32"	(2.36)	120"	(3948)
BKH-094-180	3/32"	(2.36)	180"	(4572)
BKH-094-240	3/32"	(2.36)	240"	(6096)
BKH-094-360	3/32"	(2.36)	360"	(9144)



**Box Quantity - 20**  
5 bags containing 4 pieces per bag

## KwikWire™ Single Style Hook Termination Kits

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
BKH-094-40K	3/32"	(2.36)	40"	(1016)
BKH-094-80K	3/32"	(2.36)	80"	(2032)
BKH-094-120K	3/32"	(2.36)	120"	(3948)
BKH-094-180K	3/32"	(2.36)	180"	(4572)
BKH-094-240K	3/32"	(2.36)	240"	(6096)
BKH-094-360K	3/32"	(2.36)	360"	(9144)




**Box Quantity - 20**  
5 bags containing 4 pieces per bag


## KwikWire™ 'Y' Style Hook Termination With Loop

- Hook designed to accept up to 3/8" diameter wire.
- Available as a wire rope with hook termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360".
- Available in single, double (Y), and triple (3) leg styles

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
BKYH18-094	3/32"	(2.36)	18"	(457)
BKYH30-094	3/32"	(2.36)	30"	(762)



**Box Quantity - 10**  
5 bags containing 2 pieces per bag



Read safety/installation instruction sheets in packages before use.

# Low Voltage & Communication Fasteners

## KwikWire™ 'Y' Style Hook Termination

Part Number	Leg Length		Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)	in.	(mm)
BKYH18-094-40	18"	(457)	3/32"	(2.36)	40"	(1016)
BKYH18-094-80	18"	(457)	3/32"	(2.36)	80"	(2032)
BKYH18-094-120	18"	(457)	3/32"	(2.36)	120"	(3948)
BKYH18-094-180	18"	(457)	3/32"	(2.36)	180"	(4572)
BKYH18-094-240	18"	(457)	3/32"	(2.36)	240"	(6096)
BKYH18-094-360	18"	(457)	3/32"	(2.36)	360"	(9144)
BKYH30-094-40	30"	(762)	3/32"	(2.36)	40"	(1016)
BKYH30-094-80	30"	(762)	3/32"	(2.36)	80"	(2032)
BKYH30-094-120	30"	(762)	3/32"	(2.36)	120"	(3948)
BKYH30-094-180	30"	(762)	3/32"	(2.36)	180"	(4572)
BKYH30-094-240	30"	(762)	3/32"	(2.36)	240"	(6096)
BKYH30-094-360	30"	(762)	3/32"	(2.36)	360"	(9144)



**Box Quantity - 10**  
5 bags containing 2 pieces per bag

## KwikWire™ 'Y' Style Hook Termination Kits

- Hook designed to accept up to 3/8" diameter wire.
- Available as a wire rope with loop termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360".

Part Number	Leg Length		Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)	in.	(mm)
BKYH18-094-40K	18"	(457)	3/32"	(2.36)	40"	(1016)
BKYH18-094-80K	18"	(457)	3/32"	(2.36)	80"	(2032)
BKYH18-094-120K	18"	(457)	3/32"	(2.36)	120"	(3948)
BKYH18-094-180K	18"	(457)	3/32"	(2.36)	180"	(4572)
BKYH18-094-240K	18"	(457)	3/32"	(2.36)	240"	(6096)
BKYH18-094-360K	18"	(457)	3/32"	(2.36)	360"	(9144)
BKYH30-094-40K	30"	(762)	3/32"	(2.36)	40"	(1016)
BKYH30-094-80K	30"	(762)	3/32"	(2.36)	80"	(2032)
BKYH30-094-120K	30"	(762)	3/32"	(2.36)	120"	(3948)
BKYH30-094-180K	30"	(762)	3/32"	(2.36)	180"	(4572)
BKYH30-094-240K	30"	(762)	3/32"	(2.36)	240"	(6096)
BKYH30-094-360K	30"	(762)	3/32"	(2.36)	360"	(9144)



**Box Quantity - 10**  
5 bags containing 2 pieces per bag

Read safety/installation instruction sheets in packages before use.

# Low Voltage & Communication Fasteners

## KwikWire™ Single Style Toggle Termination

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
BKT-063-40	1/16"	(1.59)	40"	(1016)
BKT-063-80	1/16"	(1.59)	80"	(2032)
BKT-063-120	1/16"	(1.59)	120"	(3948)
BKT-063-180	1/16"	(1.59)	180"	(4572)
BKT-063-240	1/16"	(1.59)	240"	(6096)
BKT-063-360	1/16"	(1.59)	360"	(9144)



**Box Quantity - 20**  
5 bags containing 4 pieces per bag

## KwikWire™ Single Style Toggle Termination Kits

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
BKT-063-40K	1/16"	(1.59)	40"	(1016)
BKT-063-80K	1/16"	(1.59)	80"	(2032)
BKT-063-120K	1/16"	(1.59)	120"	(3948)
BKT-063-180K	1/16"	(1.59)	180"	(4572)
BKT-063-240K	1/16"	(1.59)	240"	(6096)
BKT-063-360K	1/16"	(1.59)	360"	(9144)




**Box Quantity - 20**  
5 bags containing 4 pieces per bag


## KwikWire™ 'Y' Style Toggle Termination With Loop

- Available as a wire rope with toggle termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360".
- Available in single, double (Y), and triple (3) leg styles
- All triple (3) leg styles are non-stock, consult Eaton for lead times

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
BKYT12-063	1/16"	(1.59)	12"	(305)
BKYT18-063	1/16"	(1.59)	18"	(457)
BKYT30-063	1/16"	(1.59)	30"	(762)



**Box Quantity - 10**  
5 bags containing 2 pieces per bag



Triple (3) leg style

Read safety/installation instruction sheets in packages before use.

# Low Voltage & Communication Fasteners

## KwikWire™ 'Y' Style Toggle Termination

Part Number	Leg Length		Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)	in.	(mm)
BKYT12-063-40	12"	(305)	1/16"	(1.59)	40"	(1016)
BKYT12-063-80	12"	(305)	1/16"	(1.59)	80"	(2032)
BKYT12-063-120	12"	(305)	1/16"	(1.59)	120"	(3948)
BKYT12-063-180	12"	(305)	1/16"	(1.59)	180"	(4572)
BKYT12-063-240	12"	(305)	1/16"	(1.59)	240"	(6096)
BKYT12-063-360	12"	(305)	1/16"	(1.59)	360"	(9144)
BKYT18-063-40	18"	(457)	1/16"	(1.59)	40"	(1016)
BKYT18-063-80	18"	(457)	1/16"	(1.59)	80"	(2032)
BKYT18-063-120	18"	(457)	1/16"	(1.59)	120"	(3948)
BKYT18-063-180	18"	(457)	1/16"	(1.59)	180"	(4572)
BKYT18-063-240	18"	(457)	1/16"	(1.59)	240"	(6096)
BKYT18-063-360	18"	(457)	1/16"	(1.59)	360"	(9144)
BKYT30-063-40	18"	(457)	1/16"	(1.59)	40"	(1016)
BKYT30-063-80	30"	(762)	1/16"	(1.59)	80"	(2032)
BKYT30-063-120	30"	(762)	1/16"	(1.59)	120"	(3948)
BKYT30-063-180	30"	(762)	1/16"	(1.59)	180"	(4572)
BKYT30-063-240	30"	(762)	1/16"	(1.59)	240"	(6096)
BKYT30-063-360	30"	(762)	1/16"	(1.59)	360"	(9144)



**Box Quantity - 10**  
5 bags containing 2 pieces per bag

## KwikWire™ 'Y' Style Toggle Termination Kits

- Available as a wire rope with loop termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360"

Part Number	Leg Length		Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)	in.	(mm)
BKYT12-063-40K	12"	(305)	1/16"	(1.59)	40"	(1016)
BKYT12-063-80K	12"	(305)	1/16"	(1.59)	80"	(2032)
BKYT12-063-120K	12"	(305)	1/16"	(1.59)	120"	(3948)
BKYT12-063-180K	12"	(305)	1/16"	(1.59)	180"	(4572)
BKYT12-063-240K	12"	(305)	1/16"	(1.59)	240"	(6096)
BKYT12-063-360K	12"	(305)	1/16"	(1.59)	360"	(9144)
BKYT18-063-40K	18"	(457)	1/16"	(1.59)	40"	(1016)
BKYT18-063-80K	18"	(457)	1/16"	(1.59)	80"	(2032)
BKYT18-063-120K	18"	(457)	1/16"	(1.59)	120"	(3948)
BKYT18-063-180K	18"	(457)	1/16"	(1.59)	180"	(4572)
BKYT18-063-240K	18"	(457)	1/16"	(1.59)	240"	(6096)
BKYT18-063-360K	18"	(457)	1/16"	(1.59)	360"	(9144)
BKYT30-063-40K	18"	(457)	1/16"	(1.59)	40"	(1016)
BKYT30-063-80K	30"	(762)	1/16"	(1.59)	80"	(2032)
BKYT30-063-120K	30"	(762)	1/16"	(1.59)	120"	(3948)
BKYT30-063-180K	30"	(762)	1/16"	(1.59)	180"	(4572)
BKYT30-063-240K	30"	(762)	1/16"	(1.59)	240"	(6096)
BKYT30-063-360K	30"	(762)	1/16"	(1.59)	360"	(9144)



**Box Quantity - 10**  
5 bags containing 2 pieces per bag

Read safety/installation instruction sheets in packages before use.

# Low Voltage & Communication Fasteners

## KwikWire™ Bolt Termination


- Ideal for use with ARS, ARC, ADI, ACPW, or ACPD anchors.
- Available as a wire rope with bolt termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360".
- Available in single, double (Y), and triple leg (3) styles
- All (Y) and triple (3) styles are non-stock, consult Eaton for lead times

Part Number	Thread Size	Wire Rope Diameter		Length	
		in.	(mm)	in.	(mm)
<b>BKB25-063-40</b>	¼"-20	¼"	(1.59)	40"	(1016)
<b>BKB25-063-80</b>	¼"-20	¼"	(1.59)	80"	(2032)
<b>BKB25-063-120</b>	¼"-20	¼"	(1.59)	120"	(3948)
<b>BKB25-063-180</b>	¼"-20	¼"	(1.59)	180"	(4572)
<b>BKB25-063-240</b>	¼"-20	¼"	(1.59)	240"	(6096)
<b>BKB25-063-360</b>	¼"-20	¼"	(1.59)	360"	(9144)
<b>BKB38-094-40</b>	⅜"-16	⅜"	(2.36)	40"	(1016)
<b>BKB38-094-80</b>	⅜"-16	⅜"	(2.36)	80"	(2032)
<b>BKB38-094-120</b>	⅜"-16	⅜"	(2.36)	120"	(3948)
<b>BKB38-094-180</b>	⅜"-16	⅜"	(2.36)	180"	(4572)
<b>BKB38-094-240</b>	⅜"-16	⅜"	(2.36)	240"	(6096)
<b>BKB38-094-360</b>	⅜"-16	⅜"	(2.36)	360"	(9144)




### Box Quantity - 20

5 bags containing 4 pieces per bag



Double (Y) leg style



Triple (3) leg style

## KwikWire™ Bolt Termination Kits

- Ideal for use with ARS, ARC, ADI, ACPW, or ACPD anchors.
- Available as a wire rope with bolt termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360".
- Available in single, double (Y), and triple (3) styles
- All double (Y) and triple (3) styles are non-stock, consult Eaton for lead times

Part Number	Thread Size	Wire Rope Diameter		Length	
		in.	(mm)	in.	(mm)
<b>BKB25-063-40K</b>	¼"-20	¼"	(1.59)	40"	(1016)
<b>BKB25-063-80K</b>	¼"-20	¼"	(1.59)	80"	(2032)
<b>BKB25-063-120K</b>	¼"-20	¼"	(1.59)	120"	(3948)
<b>BKB25-063-180K</b>	¼"-20	¼"	(1.59)	180"	(4572)
<b>BKB25-063-240K</b>	¼"-20	¼"	(1.59)	240"	(6096)
<b>BKB25-063-360K</b>	¼"-20	¼"	(1.59)	360"	(9144)
<b>BKB38-094-40K</b>	⅜"-16	⅜"	(2.36)	40"	(1016)
<b>BKB38-094-80K</b>	⅜"-16	⅜"	(2.36)	80"	(2032)
<b>BKB38-094-120K</b>	⅜"-16	⅜"	(2.36)	120"	(3948)
<b>BKB38-094-180K</b>	⅜"-16	⅜"	(2.36)	180"	(4572)
<b>BKB38-094-240K</b>	⅜"-16	⅜"	(2.36)	240"	(6096)
<b>BKB38-094-360K</b>	⅜"-16	⅜"	(2.36)	360"	(9144)



### Box Quantity - 20

5 bags containing 4 pieces per bag



Double (Y) leg style



Triple (3) leg style

Read safety/installation instruction sheets in packages before use.

# Low Voltage & Communication Fasteners

Low voltage & communication fasteners

## KwikWire™ Angle Bracket Termination

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
<b>BKA-063-40</b>	1/16"	(1.59)	40"	(1016)
<b>BKA-063-80</b>	1/16"	(1.59)	80"	(2032)
<b>BKA-063-120</b>	1/16"	(1.59)	120"	(3948)
<b>BKA-063-180</b>	1/16"	(1.59)	180"	(4572)
<b>BKA-063-240</b>	1/16"	(1.59)	240"	(6096)
<b>BKA-063-360</b>	1/16"	(1.59)	360"	(9144)



**Box Quantity - 20**  
5 bags containing 4 pieces per bag

## KwikWire™ Angle Bracket Termination Kits

- Available as a wire rope with angle bracket termination only or as a ready-to-use kit with a BKC100 clamp.
- Available in lengths of 40", 80", 120", 180", 240", and 360".

Part Number	Wire Rope Diameter		Length	
	in.	(mm)	in.	(mm)
<b>BKA-063-40K</b>	1/16"	(1.59)	40"	(1016)
<b>BKA-063-80K</b>	1/16"	(1.59)	80"	(2032)
<b>BKA-063-120K</b>	1/16"	(1.59)	120"	(3948)
<b>BKA-063-180K</b>	1/16"	(1.59)	180"	(4572)
<b>BKA-063-240K</b>	1/16"	(1.59)	240"	(6096)
<b>BKA-063-360K</b>	1/16"	(1.59)	360"	(9144)



**Box Quantity - 20**  
5 bags containing 4 pieces per bag