


## Straight Blade Power Devices - 20, 30, 50 & 60A



Rating: Amps V/AC	Receptacle/ Plug NEMA Configuration	Flush Receptacles	Wallplate	Surface Receptacle	Panel Mount Receptacle	Plugs	Angle Plugs
<b>3-Pole, 4-Wire Grounding</b>							
20A 125/250V	 14-20R	 14-20P	Industrial: <b>5759</b> (Black)				
30A 125/250V Dryer	 14-30R	 14-30P	Commercial: <b>1257</b> (Black)	Standard Size: 39CH, 68, 2068, 2168, 93221, 93227  Mid-Size: 5068, PJ703, PJ724	Commercial: <b>1225</b> (Black)	Industrial: <b>5746N</b> (Gray)	Commercial: <b>S21</b> (Black)
			Industrial: <b>5744N</b> (Black)				Standard Size: 69, 5169, 93223
30A 3Ø 250V	 15-30R	 15-30P	Industrial: <b>8430N</b> (Black)	Standard Size: 69, 5169, 93223		Industrial: <b>8432N</b> (Gray)	Industrial: <b>8432AN</b> (Gray)
50A 125/250V Range	 14-50R	 14-50P	Commercial: <b>1258</b> (Black)	Standard Size: 39CH, 68, 2068, 2168, 93221, 93227  Mid-Size: 5068, PJ703, PJ724	Commercial: <b>1212</b> (Black)	Commercial: <b>58</b> (Black)	Industrial: <b>5745N</b> (Gray)
			Industrial: <b>5754N</b> (Black)				Standard Size: 69, 5169, 93223
50A 3Ø 250V	 15-50R	 15-50P	Industrial: <b>8450N</b> (Black)	Standard Size: 69, 5169, 93223		Industrial: <b>8452N</b> (Gray)	Industrial: <b>8452AN</b> (Gray)
60A 125/250V	 14-60R	 14-60P	Industrial: <b>9460N</b> (Black)	Standard Size: 69, 5169, 93223		Commercial: <b>60</b> (Black)	Commercial: <b>S20</b> (Black)
							Industrial: <b>9462AN</b> (Gray)
60A 3Ø 250V	 15-60R	 15-60P	Industrial: <b>8460N</b> (Black)	Standard Size: 69, 5169, 93223		Industrial: <b>AH8462N</b> (Gray)	Industrial: <b>AH8462AN</b> (Gray)
<b>4-Pole, 4-Wire Non-Grounding</b>							
30A 3ØY 120/208V	 18-30R	 18-30P				Industrial: <b>8332N</b> (Gray)	Industrial: <b>8332AN</b> (Gray)
50A 3ØY 120V/208V	 18-50R	 18-50P				Industrial: <b>8352N</b> (Gray)	Industrial: <b>8352AN</b> (Gray)
60A 3ØY 120/208V	 18-60R	 18-60P	Industrial: <b>5515N</b> (Black)	Standard Size: 69, 5169, 93223			Commercial: <b>S19</b> (Black)
							Industrial: <b>5517N</b> (Gray)

## Range & Dryer Power Plugs

3-Pole, 3-Wire Non-Grounding  
30A, 125/250V/AC  
50A, 125/250V/AC



10-30P

10-50P

### FEATURES

- For replacement use in older homes with 3-wire range and dryer connection points.
- Universal plugs include blades for both 30A and 50A configurations of the same voltage.
- Terminals have pressure plates to protect wires.
- Body made of abuse-resistant thermoplastic.
- Accepts #10 - #8 AWG wire.



S80

## Universal Power Plugs


30A 125/250V/AC or 50A 125/250V/AC

Description	Color	Catalog No.		Matching Receptacles
Universal 30A or 50A Angled NEMA 10-30P/10-50P Range or Dryer Power Plug	Black	<input type="checkbox"/> S80	•	30A: 32B, 38B 50A: 112, 125

Listed to UL498, file no. E15012; NOM certified

## Range & Dryer Power Plugs

3-Pole, 4-Wire Grounding  
30A, 125/250V/AC  
50A, 125/250V/AC



14-30P

14-50P

### FEATURES

- For replacement use in newer homes with 4-wire range and dryer connection points.
- Universal plugs include blades for both 30A and 50A configurations of the same voltage.
- Terminals have pressure plates to protect wires.
- Body made of abuse-resistant thermoplastic.
- Accepts #10 - #4 AWG wire.



S21

## Universal Power Plugs

30A 125/250V/AC or 50A 125/250V/AC

Description	Color	Catalog No.		Matching Receptacles
Universal 30A or 50A Angled NEMA 14-30P/14-50P Range or Dryer Power Plug	Black	<input type="checkbox"/> S21	•	30A: 1257, 1258 50A: 1212, 1225


cULus Listed to UL498, file no. E15012; NOM certified

**Dimensional Information:** B-62

**Specification Information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)

**NAFTA Compliant:** See page F-21

## Power Devices, Flush Receptacles



Cat. Nos.	A	B	C	D (depth)	E	F (face dia.)
30 & 1200 Series	3.28" (83.3mm)	2.38" (60.5mm)	1.81" (46.0mm)	1.42" (36.1mm)	2.50" (63.5mm)	2.10" (53.5mm)

## Power Devices, Surface Receptacles




Cat. Nos.	A	B	C
100 & 1200 Series	2.10" (53.3mm)	4.75" (120.7mm)	2.50" (63.5mm)

## Power Devices, Panel Mount Receptacles




Cat. Nos.	A	B
58, 60	2.80" (71.1mm)	2.80" (71.1mm)
U1263	1.69" (42.9mm)	2.09" (53.1mm)

## Power Devices, Angled Plugs




Cat. Nos.	A	B	C	Cord Dia.
S80 & 83	2.92" (74.2mm)	1.03" (26.2mm)	2.80" (71.1mm)	S80: 0.80" (20.3mm) max. 83: 0.64" (16.3mm) max.
S41 & S42 S20 & S21	3.37" (85.6mm)	1.38" (35.1mm)	2.87" (72.9mm)	S41 & S42: 1.10" (27.9mm) S20 & S21: 1.13" (28.7mm)

## Miscellaneous Power Devices



805V




2836

## Heavy Duty Grade Connectors



Family	A	B	C	Cord Dia.
QuickGrip™	1.40" (35.6mm)	2.57" (65.4mm)	1.65" (42.0mm)	0.22-0.66" (5.6-16.8mm)
Armored Vinyl	1.35" (34.3mm)	2.60" (66.0mm)	1.50" (38.1mm)	0.25-0.63" (6.4-15.9mm)
Vinyl	1.35" (34.3mm)	2.61" (66.3mm)	1.54" (39.1mm)	0.25-0.66" (6.4-16.6mm)
Rubber	1.36" (34.5mm)	2.90" (73.7mm)	1.54" (39.1mm)	0.25-0.60" (6.4-15.2mm)

## Heavy Duty Grade Plugs



Family	A	B	C	D	Cord Dia.
QuickGrip™	1.40" (35.6mm)	1.95" (49.7mm)	1.68" (42.6mm)	-	0.22-0.66" (5.6-16.8mm)
Armored Vinyl	1.65" (41.9mm)	1.93" (49.0mm)	1.87" (47.4mm)	-	0.25-0.63" (6.4-15.9mm)
Vinyl	1.65" (41.9mm)	1.54" (39.1mm)	-	-	0.25-0.66" (6.4-16.8mm)
Angled Vinyl	1.25" (31.8mm)	1.42" (36.1mm)	1.50" (38.1mm)	1.95" (49.5mm)	0.25-0.66" (6.4-16.8mm)
Rubber	1.54" (39.1mm)	2.00" (50.8mm)	-	-	0.25-0.60" (6.4-15.2mm)