

lifeAGLOW®

HINKLEY

L I G H T I N G

HINKLEY

L I G H T I N G

INTERIOR | BATH | OPEN AIR | OUTDOOR
FOR LANDSCAPE LIGHTING, VISIT HINKLEYLIGHTING.COM OR REFER TO
THE FULL LINE HINKLEY LANDSCAPE LIGHTING CATALOG.

VIEW FREDRICK RAMOND, HINKLEY'S LUXURY LINE,
AT FREDERICKRAMOND.COM

CULTURED
AND CLASSIC.
WARM AND
REFRESHING.

Welcome to Hinkley.





CELEBRATING
95 YEARS
OF DESIGN
EXCELLENCE

FROM LEFT:
ERIC WIEDEMER | VICE PRESIDENT AND
GENERAL COUNSEL
RICK WIEDEMER | CEO
JESS WIEDEMER | PRESIDENT AND COO

Hinkley Lighting, Inc. Global Headquarters
Avon Lake, Ohio

A FRESH PERSPECTIVE

WE'RE CONSTANTLY SEEKING OUT NEW WAYS TO IMPROVE YOUR HOME AND LIFESTYLE.

To get it right, we integrate the latest innovations in technology, quality, customer care and design, making sure our products and our people stay cutting-edge. Keeping a fresh perspective allows us to both inspire and inform your choices (we know your time is precious) and give you the confidence and clarity to choose products that are right for you. This quest to stay one step ahead is one of the reasons we love what we do. Knowledge is power, and our goal is to guide you in a way that seamlessly merges solutions with style.

Explore this catalog and take advantage of our easy-to-understand product specifications, breathtaking photography and designer tips. We want you to enjoy a superb and supportive digital experience as well, so we offer all this and more at hinkleylighting.com, across our social platforms and via our Hinkley iPad app. Our brands extend beyond Hinkley, to our luxury line Fredrick Ramond as well as Hinkley Landscape Lighting, to fulfill a complete range of lighting desires.

We have been around a long time, and we've learned a few things along the way... and one of the most important is that meaningful experiences with our products and our people is what matters most. We hope you find our perspective, and our products, refreshing. We are here for you, and we aim to serve.



Rick Wiedemer

RICK WIEDEMER CEO

CONTENTS



INTERIOR COLLECTIONS



BATH COLLECTIONS

ACADEMY	088	HARPER	314
ALISTER	240	HARRISON	180
AMELIA	081	HATHAWAY	186
ASCHER	158	HEYWOOD	052
ASTRID	126	HOWELL	120
ATRIUM	124	LANZA	304
AVENUE	305	LARA	160
BARSTOW	079	LARCHMERE	162
BECKETT	054	LATITUDE	198
BLAKELY	164	MARCELLINA	294
BOLLA	202	MARGEAUX	152
BOYER	140	MARLOWE	113
BRANTLEY	220	MAXWELL	310
CAMBRIDGE	296	MERCER	303
CARLTON	292	MERIDIAN	193
CARTWRIGHT	060	MIDDLETON	064
CASA	266	MIDTOWN	196
CHARLOTTE	182	MONDRIAN	200
CLANCY	074	MORGAN	228
CLARENDON	236	ODEON	122
COLBIN	311	PLANTATION	284
COLLIER	114	PLYMOUTH	278
CONGRESS	091	PULLMAN	073
CORDILLERA	264	QUENTIN	128
DAKOTA	068	REFINERY	110
DENTON	056	RIGBY	107
ELAINE	254	ROCKFORD	300
ELEANOR	246	RUTHERFORD	244
ELLIOTT	078	SABINA	226
ELROY	080	SOMERSET	123
EUCLID	148	SORRENTO	265
FENMORE	072	SURREY	232
FINLEY	112	SUSSEX	272
FLEMING	239	TERRA	146
FLETCHER	086	THEORY	125
FULHAM	144	TRUMAN	224
FULTON	132	WAVERLY	234
GATSBY	104	WESTON	312
GENTRY	256	WEXLEY	252
HADLEY	306	WYATT	058
HALSEY	313	ZELDA	156
HAMPTON	168		

ABBIE	405	SIMI	320
ACCLAIM	322	TAYLOR	346
AINSLEY	380	TESSA	353
ALICE	392	THISTLEDOWN	400
ASHLEY	384	TREMONT	325
AVON	349	UNITY	324
BALDWIN	394	VERVE	342
BENNETT	366	WINTON	328
BLYTHE	412	YORKTOWN	408
BOLLA	386		
BOYER	368		
BRANTLEY	414		
BROOKE	416		
CASA	422		
CHLOE	338		
CLANCY	373		
COLETTE	402		
CONGRESS	374		
DAPHNE	335		
DARBY	397		
DARIA	332		
FAIRLANE	326		
FAYE	383		
FRANCOISE	420		
JACKSON	370		
JOSIE	385		
KARLIE	358		
KYRA	356		
LANZA	343		
LATITUDE	339		
LAUREL	360		
MERIDIAN	364		
MILA	330		
MILEY	354		
PINNACLE	362		
PLANTATION	424		
PORTIA	323		
REESE	419		
RIGBY	378		
SADIE	396		
SAN SIMEON	426		
SHELLY	410		



OUTDOOR COLLECTIONS

ADAIR	576	LUNA	462	VAPOR	448
ALFORD PLACE	596	MANHATTAN	504	VISTA	455
ANCHORAGE	578	MANOR HOUSE	642	VUE	454
ARIA	484	MARINA	554	WABASH	640
ATLANTIS	472	MIST	450	WALKER	540
ATWELL	438	MONDRIAN	533	WESTPORT	549
AUGUSTA	658	MONTAUK	589	WESTWINDS	624
BARRINGTON	627	MONTICELLO	656	WINDSOR	632
BECKETT	433	NANTUCKET	588	YORK	582
BELDEN PLACE	569	NEW CASTLE	560		
BINGHAM	584	NEWPORT	548	LUNA STEP	666
BOLLA	610	OXFORD	636	NUVI HARDSCAPE	668
BRIGGS	571	PERRY	550		
BROMLEY	604	PLANTATION	620		
BURKE	538	PLAZA	453		
BURTON	544	PORTER	572	ICONS & FINISHES	006
CALISTOGA	563	QUINCY	530	TECHNOLOGY	007
CAMELOT	644	RALEY	628	LET'S CONNECT	008
CAPE COD	564	RANDOLPH	524	DESIGNER COLLECTIVE	009
CARSON	440	REEF	552	PICTORIAL INDEX	012
CASA	614	REGAL	645	LANDSCAPE LIGHTING	668
CASCADE	470	REVERE	590	INDEX	671
CASTELLE	520	RILEY	532		
CHERRY CREEK	514	SAN CLEMENTE	652		
CLIFTON PARK	660	SATURN	496		
COLFAX	502	SAYBROOK	568		
DORIAN	480	SEDGWICK	593		
EDGEWATER	646	SENATOR	641		
ENZO	608	SHELTER	488		
FREEPORT	556	SORRENTO	618		
GLACIER	446	SULLIVAN	534		
HADLEY	528	SURF	456		
HARBOR	508	SUTCLIFFE	546		
HORIZON	494	TAHOE	526		
HUDSON	529	TATUM	570		
KEY WEST	650	THATCHER	545		
KORE	468	THEO	537		
KUBE	479	TITAN	471		
LEDGEWOOD	518	TRAFALGAR	638		
LEX	460	TRELLIS	598		
LINCOLN	594	TROYER	436		
LUCERNE	662	TUCKER	522		

“Lighting needs to have personality and should emulate a signature style, whether it stands alone or is integrated into the design of a space.”















LISA MCDENNON
LISAMCDENNONDESIGN.COM
LAGUNA BEACH, CA

Meet Hinkley's Designer Collective **PAGE 9**

ICONS & FINISH REFERENCES

Throughout this catalog we have utilized a variety of important icons and finish codes to assist you with your lighting selections. Below is a key describing each of these icons in detail as well as a list of our extensive product finishes with abbreviated codes for easy reference.

ICON DESCRIPTIONS

- 
ADA COMPLIANT
 Indicates fixtures that adhere to the standards and guidelines listed by the Americans with Disabilities Act.
- 
COMBINATION MOUNT
 Indicates fixtures that are supplied with the means to be chain hung or mounted flush to the ceiling.
- 
DARK SKY
 Indicates fixtures that are engineered to minimize light glare upward into the night sky.
- 
DIFFUSER INCLUDED
 Indicates fixtures that come equipped with a diffuser to minimize bulb exposure and soften the intensity of light emitted.
- 
FIXTURE EXCEEDS 50 LBS.
 Indicates fixtures weighing over 50 lbs. Fixtures must be supported independently of the outlet box unless the outlet box is UL listed for the appropriate weight. Required hardware included.
- 
INVISI-MOUNT
 Indicates fixtures where the mounting hardware is hidden on the back plate.
- 
LED
 Fixtures supplied with fully integrated LEDs and drivers or specifically matched LED lamps based on performance and application.
- 
QUICKFIT
 Fixtures recommended for use with QuickFit recessed can light converter kit.
- 
OPEN AIR
 Indicates fixtures that are appropriate and rated for both interior and exterior applications.
- 
OVAL-SHAPED FIXTURE
 Indicates chandeliers that are oval in shape.
- 
SELECT-A-LITE
 Indicates fixtures that come with sockets that can accept either candelabra or medium-based bulbs.
- 
TITLE 24
 Meets California Energy Commission Title regulations.

FINISH CODES AND NAMES

AI	AGED IRON	MT	METRO BRONZE
AN	ANTIQUE NICKEL	OB	OLDE BRONZE
AP	ANTIQUE COPPER	OL	OLDE BLACK
AR	ANCHOR BRONZE	OP	OLDE PENNY
AS	AGED BRASS	OR	OILED BRONZE
BB	BURNISHED BRASS	OZ	OIL RUBBED BRONZE
BC	BRUSHED CAMEL	PB	POLISHED BRASS
BG	BLACK GRANITE	PL	POLISHED ANTIQUE NICKEL
BK	BLACK	PN	POLISHED NICKEL
BN	BRUSHED NICKEL	PS	POLISHED STAINLESS STEEL
BR	BRUSHED BRONZE	PT	POLISHED WHITE
BV	BRUSHED SILVER	PW	PEWTER
BZ	BRONZE	PZ	PEARL BRONZE
CB	COPPER BRONZE	RB	REGENCY BRONZE
CG	CEMENT GRAY	RI	RUSTIC IRON
CM	CHROME	RK	RIVER ROCK
CW	CLASSIC WHITE	RS	RUSTIC BRASS
DG	DELUXE GOLD	RY	ROYAL BRONZE
DZ	AGED ZINC	SB	SPANISH BRONZE
EN	ENGLISH NICKEL	SK	SATIN BLACK
EZ	ENGLISH BRONZE	SL	SILVER LEAF
FB	FORUM BRONZE	SN	SIENNA
FZ	FRENCH BRONZE	SQ	SEQUIOA
GF	ANTIQUE GOLD LEAF	SS	STAINLESS STEEL
GR	GOLDEN BRONZE	ST	SANDSTONE
GS	GREYSTONE	SW	SATIN WHITE
GV	GALVANIZED	SZ	SIENNA BRONZE
GZ	GRAPHITE BRONZE	TT	TITANIUM
HB	HERITAGE BRASS	TZ	TEXTURED BRONZE
HE	HEMATITE	VI	VINTAGE IRON
HR	HEIRLOOM BRASS	VK	VINTAGE BLACK
IN	INDUSTRIAL IRON	VS	VINTAGE BRASS
IR	IRON RUST	VZ	VICTORIAN BRONZE
KZ	BUCKEYE BRONZE	WT	WARM WHITE
LA	LIGHT ALMOND	WZ	WEATHERED ZINC
LZ	LIGHT OILED BRONZE		
MB	MUSEUM BLACK		
MC	METRO COPPER		
MM	METALLIC MATTE BRONZE		
MN	MIDNIGHT BRONZE		
MO	MOCHA		
MR	MUSEUM BRONZE		

ECO-CHIC LIGHTING

Energy-efficient lighting products engineered with exceptional design and creativity.



THE SHELTER COLLECTION | 1325BK, PAGE 488



LED FILAMENT BULBS

MODERN TECHNOLOGY MOVES BEYOND MODERN STYLES!

Popular Outdoor fixtures with candelabra base lamping are now offered with the energy-efficiency of LED filament bulbs. These 5w candelabra lamps provide exceptional aesthetic appeal comparable to the soft glow of an incandescent bulb with the cost and energy-saving power of LED. Ensure your favorite traditional designs are up-to-date with the latest lamping option by looking for item numbers with a -LL suffix.

LED PERFORMANCE SPECIFICATIONS

Many technical elements factor into selecting a fixture, and learning the lingo behind LED performance is helpful in choosing your lighting. You will see the following need-to-know terms in product specs:

LUMENS The measure of the total “amount” of visible light emitted from a lamp or fixture.

COLOR TEMPERATURE The comparative color appearance of a light source, measured in Kelvin (K).

CRI (Color Rendering Index) The quality of light in how objects exhibit color compared to incandescent lamps.

INCANDESCENT EQUIVALENCY Resulting light intensity similar to same incandescent fixture with this wattage lamp.

“Lighting doesn’t need to be overpowering to be effective—in fact, often less is more. With the advances in LED technology it has become so easy to be eco-conscious without sacrificing style.”



NICK MCCULLOUGH
MCCULLOUGH'S LANDSCAPE
AND NURSERY
COLUMBUS, OH

Meet Hinkley's Designer Collective **PAGE 9**

#hinkleystyle



FOLLOW @HINKLEYLIGHTING FOR THE LATEST IN LIGHTING, STYLE, DÉCOR AND MORE!

Social media is the ultimate creative platform—a community of individuals, influencers and brands connected by a show and tell ideology. And most of all, it's fun! We invite you to join our social circle, where we share our passion for stylishly curated living.

SHARE THE LOVE


Show off that chic space of yours on Instagram with #hinkleystyle! We love to repost images of fixtures in their new environments, and want to thank you for welcoming Hinkley into your home.

Look for our InstaFave features throughout this catalog for the most stylish spaces illuminated by Hinkley fixtures. >

@INSTAFAVE



@andreaporritt
THE MARGEUX COLLECTION



Go ahead, **APPLAUD!**

Find lighting you will love with Hinkley's signature mix of products, design inspiration and lighting tips. Illuminate indoor and outdoor spaces with ease by browsing our source book, curated style guides and how-to videos, and even locate your preferred lighting showroom in a snap!



TO DOWNLOAD ON YOUR IPAD,
SEARCH "HINKLEY LIGHTING"
IN THE APP STORE.

Meet Hinkley Lighting's

DESIGNER COLLECTIVE

We've partnered with celebrated designers, stylists and bloggers who share our passion for the art of living well. These highly connected influencers bring you the most innovative expertise in the interiors industry. Look for their design savvy contributions throughout these pages and up the ante in your own style game!

GET YOUR DAILY DOSE OF THE DESIGNER COLLECTIVE'S SIGNATURE STYLE BY FOLLOWING @HINKLEYLIGHTING AND EACH CONTRIBUTOR ON INSTAGRAM.



KELLY DECK

KELLY DECK DESIGN | VANCOUVER, BC
@kellydeckdesign



MARIE FLANIGAN

MARIE FLANIGAN INTERIORS | HOUSTON, TX
@marieflaniganinteriors



ERIKA HOLLINSHEAD WARD

ERIKA WARD INTERIORS | ATLANTA, GA
@mrsrikaward



NICK MCCULLOUGH

MCCULLOUGH'S LANDSCAPE & NURSERY | COLUMBUS, OH
@nickmccland



LISA MCDENNON

LISA MCDENNON DESIGN | LAGUNA BEACH, CA
@lisamcdennon



BECKI OWENS

BECKIOWENS.COM | SOUTHERN CALIFORNIA
@beckiowens



JILL SHARP WEEKS

JILL SHARP STUDIO | CHARLESTON, SC
@jillsharpstudio
PHOTO: BJORN WALLANDER

HEAD TO HINKLEYLIGHTING.COM FOR FULL BIOS ON EACH DESIGNER COLLECTIVE CONTRIBUTOR.





REDEFINING LUXURY | JANUARY 2018



ALISTER
Pages 240-241
Antique Nickel



ALISTER
Pages 242-243
Buckeye Bronze



ASCHER
Page 158
Brushed Caramel



ASCHER
Page 159
Polished Nickel



ASTRID
Page 126
Deluxe Gold



ASTRID
Page 127
Metallic Matte Bronze



ATRIUM
Page 124
Bronze



ATWELL
Page 439
Aged Zinc
1



ATWELL
Page 438
Oil Rubbed Bronze
1



BECKETT
Pages 54-55
Iron Rust



BECKETT
Page 433
Iron Rust
1



BLAKELY
Pages 164-165
Brushed Nickel



BLAKELY
Pages 166-167
Buckeye Bronze



BOLLA
Pages 214-215
Brushed Bronze



BOLLA
Pages 216-219
Brushed Nickel



BOLLA
Pages 210-213
Olde Bronze



BOLLA
Pages 202-205
Olde Bronze



BOLLA
Pages 206-209
Olde Bronze



BOYER
Pages 140-141
Aged Zinc



BOYER
Pages 142-143
Oil Rubbed Bronze



BRANTLEY
Pages 220-221
Brushed Nickel



BRANTLEY
Pages 222-223
Oil Rubbed Bronze



CAMBRIDGE
Pages 296-297
Burnished Brass



CAMBRIDGE
Page 299
Olde Bronze



CAMBRIDGE
Page 298
Pewter



CARLTON
Pages 292-293
Silver Leaf



CARSON
Pages 442-443
Vintage Iron



CARSON
Pages 440-441
Weathered Zinc



CARTWRIGHT
Page 62
Galvanized



CARTWRIGHT
Pages 60-61
Polished Antique Nickel



CARTWRIGHT
Page 63
Rustic Brass



CASA
Pages 268-271
Olde Black



CASA
Pages 266-267
Olde Black



CHARLOTTE
Page 183
Antique Nickel



CHARLOTTE
Page 182
Brushed Caramel



CHARLOTTE
Page 184
Chrome



CLANCY
Page 74
Aged Zinc



CLANCY
Page 77
Brushed Nickel



CLANCY
Page 76
Buckeye Bronze



CLANCY
Page 75
Polished Nickel



CLARENDON
Page 236
Aged Zinc



CLARENDON
Page 237
Bronze




COLLIER
Pages 114-115
Antique Nickel



COLLIER
Pages 118-119
Heritage Brass



COLLIER
Pages 116-117
Light Oiled Bronze



CONGRESS
Pages 101-103
Antique Nickel



CONGRESS
Pages 101-103
Chrome



CONGRESS
Pages 101-103
Oil Rubbed Bronze



CORDILLERA
Page 264
Rustic Iron



DAKOTA
Pages 68-69
Oil Rubbed Bronze



DAKOTA
Pages 70-71
Polished Antique Nickel



DENTON
Pages 56-57
Industrial Iron



ELAINE
Page 254
Light Oiled Bronze



ELAINE
Page 255
Polished Antique Nickel



ELEANOR
Pages 248-249
Heritage Brass



ELEANOR
Pages 250-251
Light Oiled Bronze



ELEANOR
Pages 246-247
Polished Antique Nickel



EUCLID
Pages 148-149
Cement Gray



EUCLID
Pages 150-151
Spanish Bronze



FENMORE
Page 72
Textured Bronze



FLEMING
Page 239
Polished Antique Nickel



FULHAM
Page 144
Buckeye Bronze



FULHAM
Page 145
Polished Antique Nickel




FULTON
Pages 132-135
Aged Zinc



FULTON
Pages 136-139
Bronze



GATSBY
Page 104
Heritage Brass



GATSBY
Page 105
Polished Antique Nickel



GENTRY
Pages 260-261
Heirloom Brass



GENTRY
Pages 262-263
Olde Bronze



GENTRY
Pages 258-259
Pewter



GENTRY
Pages 256-257
Polished Nickel



HAMPTON
Pages 168-171
Antique Nickel



HAMPTON
Pages 171-175
Brushed Bronze



HAMPTON
Pages 176-179
Buckeye Bronze



HARRISON
Pages 180-181
Buckeye Bronze





HATHAWAY
Pages 190-191
Antique Nickel
174



HATHAWAY
Pages 186-187
Olde Bronze
174



HATHAWAY
Pages 188-189
Olde Bronze
174



HEYWOOD
Pages 52-53
Weathered Zinc



HOWELL
Page 120
Oil Rubbed Bronze



LARA
Pages 160-161
Brushed Silver



LARCHMERE
Pages 162-163
English Nickel



LATITUDE
Page 198
Brushed Nickel



LATITUDE
Page 199
Oil Rubbed Bronze



MARCELLINA
Pages 294-295
Golden Bronze



MARGEUX
Pages 154-155
Polished Nickel



MARGEUX
Pages 152-153
Vintage Brass



MERIDIAN
Pages 193-195
Brushed Nickel



MIDDLETON
Pages 66-67
Graphite Bronze



MIDDLETON
Pages 64-65
Polished Nickel



MIDTOWN
Pages 196-197
Brushed Nickel



MONDRIAN
Pages 200-201
Buckeye Bronze



MORGAN
Pages 230-231
Antique Nickel



MORGAN
Pages 228-229
Brushed Bronze



PLANTATION
Pages 287-289
Burnished Brass



PLANTATION
Pages 284-286
Pearl Bronze



PLANTATION
Pages 290-291
Polished Antique Nickel



PLYMOUTH
Pages 281-283
Olde Bronze



PLYMOUTH
Pages 278-280
Polished Antique Nickel



QUENTIN
Pages 130-131
Aged Zinc



QUENTIN
Pages 128-129
Buckeye Bronze



REFINERY
Pages 110-111
Black



RIGBY
Page 108
Aged Zinc



RIGBY
Page 109
Buckeye Bronze



RIGBY
Page 107
Polished Nickel



ROCKFORD
Pages 300-301
Forum Bronze



RUTHERFORD
Pages 244-245
Oil Rubbed Bronze



SABINA
Pages 226-227
Silver Leaf



SAWYER
Pages 434-435
Sequoia



SORRENTO
Page 265
Aged Iron



SURREY
Pages 232-233
Polished Nickel



SUSSEX
Pages 272-274
Brushed Nickel



SUSSEX
Pages 275-277
English Bronze



TERRA
Page 146
Oiled Bronze



TERRA
Page 147
Polished Nickel



THEORY
Page 125
Aged Zinc



TRUMAN
Pages 224-225
Antique Nickel



WAVERLY
Page 235
Oil Rubbed Bronze



WAVERLY
Page 234
Warm White



WEXLEY
Pages 252-253
Heritage Brass



WEXLEY
Pages 252-253
Oil Rubbed Bronze



WEXLEY
Pages 252-253
Polished Nickel



WYATT
Pages 58-59
Iron Rust



ZELDA
Page 156
Polished Nickel



ZELDA
Page 157
Vintage Brass



5850
Abbie, Pages 405, 406, 407
6¾" W, 7¾" H
Brushed Caramel,
Brushed Nickel, Chrome



67001
Academy, Page 90
5½" W, 15½" H
English Nickel,
Oil Rubbed Bronze



67002
Academy, Page 90
10" W, 12½" H
English Nickel,
Oil Rubbed Bronze



67003
Academy, Page 90
6½" W, 13" H
English Nickel,
Oil Rubbed Bronze



56550
Ainsley, Pages 380, 381, 382
6¼" W, 7½" H
Brushed Nickel, Buckeye
Bronze, Polished Nickel



5830
Alice, Pages 392, 393
5¼" W, 8¾" H
Antique Nickel,
Brushed Bronze



4750
Ascher, Pages 158, 159
4¾" W, 17¾" H
Brushed Caramel,
Polished Nickel



4752
Ascher, Pages 158, 159
12" W, 17¾" H
Brushed Caramel,
Polished Nickel



5190CM
Ashley, Page 384
5" W, 8½" H
Chrome



1110
Atwell, Pages 438, 439
11½" W, 11¾" H
Aged Zinc,
Oil Rubbed Bronze



1114
Atwell, Pages 438, 439
14½" W, 15¼" H
Aged Zinc,
Oil Rubbed Bronze



5500
Avon, Pages 349, 351, 352
7¼" W, 7½" H
Brushed Nickel, Buckeye
Bronze, Chrome



5500CM-CL
Avon, Page 350
7¼" W, 7½" H
Chrome



56670
Baldwin, Pages 394, 395
4½" W, 8¼" H
Antique Nickel, Polished
Nickel



4820IR
Beckett, Page 54
8" W, 10" H
Iron Rust



5350
Bennett, Pages 366, 367
5¼" W, 9" H
Polished Nickel, Polished
Antique Nickel



5280
Blythe, Pages 412, 413
5" W, 9" H
Antique Nickel, Polished
Nickel



4650
Bolla, Pages 203, 206, 210, 214,
218, 386, 387, 388, 389, 390
7¾" W, 8½" H
Brushed Bronze, Brushed
Nickel, Olde Bronze



4671
Pages 206, 210, 214, 218
8" W, 26" H
Brushed Nickel, Olde Bronze



4530DZ
Boyer, Page 141
7" W, 9" H
Aged Zinc



5260
Boyer, Pages 368, 369, 143
7" W, 9" H
Oil Rubbed Bronze,
Polished Nickel



4630
Brantley, Pages 221, 223,
414, 415
4¾" W, 12¼" H
Brushed Nickel, Oil Rubbed
Bronze, Olde Bronze



5000
Brooke, Pages 416, 417, 418
5¼" W, 11¾" H
Antique Nickel, Olde Bronze,
Silver Leaf



4410
Cambridge, Pages 296,
298, 299
4½" W, 10¾" H
Burnished Brass,
Olde Bronze, Pewter



4412
Cambridge, Pages 296,
298, 299
13½" W, 10¾" H
Burnished Brass,
Olde Bronze, Pewter



4640BB
Cambridge, Page 297
4½" W, 13" H
Burnished Brass



4642BB
Cambridge, Page 297
14" W, 13½" H
Burnished Brass



4772SL
Carlton, Page 293
12½" W, 19" H
Silver Leaf



29700
Carson, Pages 441, 443
10" W, 10½" H
Vintage Iron, Weathered Zinc
ⓘ



4010
Casa, Pages 267, 269,
422, 423
5" W, 10¾" H
Olde Black



4300
Casa, Pages 267, 269,
422, 423
5" W, 24" H
Olde Black



3030
Clancy, Pages 74, 75, 76, 77
6" W, 11½" H
Aged Zinc, Brushed Nickel,
Buckeye Bronze,
Polished Nickel



5440BN
Clancy, Page 373
6" W, 11½" H
Brushed Nickel



58780
Colette, Pages 402, 403, 404
6" W, 8½" H
Brushed Nickel, Chrome,
Oil Rubbed Bronze



3380
Collier, Pages 115, 117, 119
5" W, 17" H
Antique Nickel, Heritage
Brass, Light Oiled Bronze



3113
Congress, Page 93
9¼" W, 12" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3170
Congress, Pages 92, 374
8" W, 11¼" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



31700
Congress, Pages 91, 375
6½" W, 13¼" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3171
Congress, Pages 92, 374
8¾" W, 13" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3173
Congress, Pages 92, 374
7" W, 13½" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3174
Congress, Pages 92, 374
7" W, 13½" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3175
Congress, Pages 92, 374
8¾" W, 13" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3176
Congress, Pages 92, 374
8" W, 11¼" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3177
Congress, Pages 92, 374
6" W, 14" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3178
Congress, Pages 93, 377
9¾" W, 12¾" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



4090RI
Cordillera, Page 264
7½" W, 22" H
Rustic Iron



4780
Dakota, Pages 69, 71
5¾" W, 10½" H
Oil Rubbed Bronze,
Polished Antique Nickel



53010
Darby, Pages 397, 398, 399
5¾" W, 8¼" H
Brushed Caramel, Brushed
Nickel, Polished Nickel



3260IN
Denton, Page 57
5¼" W, 15¾" H
Industrial Iron



4952
Eleanor, Pages 247, 249, 251
12¾" W, 9" H
Heritage Brass, Light Oiled
Bronze, Polished Antique
Nickel



3460
Euclid, Pages 149, 151
9½" W, 20" H
Cement Gray,
Spanish Bronze



5600CM
Faye, Page 383
5¾" W, 8¾" H
Chrome



5580
Francoise, Pages 420, 421
6" W, 10¾" H
Burnished Brass,
Polished Antique Nickel



3920
Fulham, Pages 144, 145
7¾" W, 21½" H
Buckeye Bronze,
Polished Antique Nickel



3330
Fulton, Pages 134, 138
7½" W, 22¼" H
Aged Zinc, Bronze



3332
Fulton, Pages 135, 139
13½" W, 9¼" H
Aged Zinc, Bronze



3308
Hadley, Page 308
7¾" W, 4½" H
Antique Nickel, Brushed Bronze,
Chrome, Oil Rubbed Bronze



3202
Hampton, Pages 170, 174, 178
15" W, 12" H
Antique Nickel, Brushed
Bronze, Buckeye Bronze



3210
Hampton, Pages 170, 174, 178
6¾" W, 12" H
Antique Nickel, Brushed
Bronze, Buckeye Bronze



51820
Jackson, Pages 370, 371, 372
5" W, 7¼" H
Brushed Nickel, Buckeye
Bronze, Polished Nickel



5370BN
Josie, Page 385
4½" W, 8½" H
Brushed Nickel



54620
Karlie, Pages 358, 359
4½" W, 8¼" H
Brushed Nickel, Chrome



55020
Kyra, Pages 356, 357
4¾" W, 7¾" H
Brushed Nickel,
Polished Nickel



5100
Lanza, Pages 343, 344, 345
7¼" W, 12" H
Antique Nickel, Brushed
Bronze, Buckeye Bronze



5651
Latitude, Pages 198, 199,
339, 340, 341
8" W, 16" H
Brushed Nickel, Chrome,
Oil Rubbed Bronze



57550
Laurel, Pages 360-361
5" W, 8¼" H
Brushed Nickel,
Polished Nickel



4400GR
Marcellina, Page 295
6½" W, 19" H
Golden Bronze



3580
Margeaux, Pages 153, 155
4½" W, 17¾" H
Polished Nickel,
Vintage Brass



3582
Margeaux, Pages 153, 155
12¾" W, 17¾" H
Polished Nickel,
Vintage Brass



3870BN
Meridian, Page 195
5" W, 11¼" H
Brushed Nickel



5590
Meridian, Pages 195, 364, 365
5" W, 8" H
Brushed Nickel, Chrome



4970 BN
Midtown, Page 197
5" W, 8" H
Brushed Nickel



5050
Miley, Pages 354, 355
4½" W, 6½" H
Brushed Nickel, Chrome



4870
Morgan, Pages 229, 231
6" W, 12" H
Antique Nickel,
Brushed Bronze



4872
Morgan, Pages 229, 231
6" W, 26" H
Antique Nickel,
Brushed Bronze



5250
Pinnacle, Pages 362, 363
5" W, 9" H
Antique Nickel,
Chrome



4140
Plantation, Pages 286, 289
6" W, 14½" H
Burnished Brass,
Pearl Bronze



4880
Plantation, Pages 285,
288, 291
6" W, 15" H
Burnished Brass, Polished
Antique Nickel, Pearl Bronze



5310
Plantation, Pages 424, 425
5" W, 8¾" H
Burnished Brass, Polished
Antique Nickel, Pearl Bronze



4240
Plymouth, Pages 279, 282
6½" W, 14" H
Olde Bronze,
Polished Antique Nickel



56320AN
Reese, Page 419
5" W, 13½" H
Antique Nickel



4360
Rigby, Pages 107, 108, 109
10" W, 8½" H
Aged Zinc, Buckeye Bronze,
Polished Nickel



5290
Rigby, Pages 378, 379
8" W, 8¾" H
Antique Nickel,
Polished Nickel



4620FB
Rockford, Page 301
5" W, 13" H
Forum Bronze



4622FB
Rockford, Page 301
14" W, 13½" H
Forum Bronze



52230BN
Sadie, Page 396
5¾" W, 7¾" H
Brushed Nickel



FR49190SLF
San Simeon, Page 426
6" W, 24½" H
Silver Leaf



35920Z
Rutherford, Page 245
8¼" W, 11¼" H
Oil Rubbed Bronze



5010
Shelly, Pages 410, 411
5½" W, 9½" H
Brushed Nickel, Chrome



4540RB
Sloan
4¾" W, 16" H
Regency Bronze



4549RB
Sloan
5½" W, 33" H
Regency Bronze



4002PN
Surrey, Page 233
11¾" W, 15¼" H
Polished Nickel



4790
Sussex, Pages 273, 276
5" W, 18" H
Brushed Nickel, English
Bronze



4792
Sussex, Pages 273, 276
15½" W, 15¾" H
Brushed Nickel,
English Bronze



5020
Taylor, Pages 346, 347, 348
7¾" W, 6" H
Brushed Nickel, Chrome,
Buckeye Bronze



3512
Terra, Pages 146, 147
10" W, 10" H
Oiled Bronze,
Polished Nickel



57130CM
Tessa, Page 353
5¾" W, 7¾" H
Chrome



51800
Thistledown, Pages 400, 401
5¼" W, 10½" H
Brushed Nickel,
Polished Nickel



1194
Troyer, Page 437
10" W, 10" H
Aged Zinc, Black,
Oil Rubbed Bronze



4020AN
Truman, Page 225
5¼" W, 13" H
Antique Nickel



51100CM
Verve, Page 342
6¾" W, 7¼" H
Chrome



5120PB
Virginian
5½" W, 11¼" H
Polished Brass



5124PB
Virginian
11" W, 11½" H
Polished Brass



4600
Waverly, Pages 234, 235
10" W, 13" H
Oil Rubbed Bronze,
Warm White



3910IR
Wyatt, Page 59
8½" W, 12½" H
Industrial Iron



5740
Yorktown, Pages 408, 409
4¾" W, 10" H
Antique Nickel,
Brushed Bronze




3440
Zelda, Pages 156, 157
5½" W, 11¾" H
Polished Nickel,
Vintage Brass

"I love balancing rustic farmhouse details with those that are industrial and slightly unexpected, like sconces featuring geometric profiles in an antique brass finish."



MARIE FLANIGAN
MARIE FLANIGAN INTERIORS
HOUSTON, TX

RIGHT: THE COLLIER COLLECTION | 3380HB, PAGE 119





“I like to use lighting with geometric shapes, clean lines and metal finishes. Consider mid-century sconces in a sitting area or bedroom for a modern updated look.”



BECKI OWENS
BECKIOWENS.COM
SOUTHERN CALIFORNIA

LEFT: THE MERCER COLLECTION | 3650HB, PAGE 303



53842
Acclaim, Page 322
3" W, 16" H
Brushed Nickel,
Polished Nickel



3072
Alister, Pages 241, 243
9¾" W, 14¼" H
Antique Nickel,
Buckeye Bronze



61111
Avenue, Page 305
5" W, 12¾" H
Brushed Nickel,
Oil Rubbed Bronze



61033
Avenue, Page 305
5" W, 7¾" H
Brushed Nickel,
Oil Rubbed Bronze



61222
Avenue, Page 305
5" W, 8" H
Brushed Nickel,
Oil Rubbed Bronze



3610
Cambridge, Pages 297,
298, 299
14½" W, 18" H
Burnished Brass,
Olde Bronze, Pewter



52400BN
Chloe, Page 338
8½" W, 8" H
Brushed Nickel



5920
Daphne, Pages 335, 336, 337
8½" W, 9" H
Brushed Nickel,
Brushed Bronze, Chrome





54812
Fairlane, Page 326
16" W, 5" H
Brushed Nickel, Chrome



4492PL
Fleming, Page 239
8" W, 14¾" H
Polished Antique Nickel



3228
Hathaway, Pages 187, 189, 191
7" W, 3¼" H
Antique Nickel,
Olde Bronze
 



3700KZ
Harrison, Page 181
7" W, 11½" H
Buckeye Bronze



3612
Lanza, Page 304
10" W, 11½" H
Antique Nickel, Brushed
Bronze, Oil Rubbed Bronze





3560BV
Lara, Page 161
8½" W, 11½" H
Brushed Silver



3992
Latitude, Pages 198-199
8" W, 16" H
Brushed Nickel, Oil Rubbed
Bronze




5650
Latitude, Pages 339, 340, 341
5" W, 8" H
Brushed Nickel, Chrome,
Oil Rubbed Bronze
 



3650
Mercer, Page 303
6¾" W, 6¾" H
Antique Nickel, Heritage
Brass, Oil Rubbed Bronze,
Polished Nickel



53550
Mila, Pages 330, 331
7¾" W, 10" H
Brushed Nickel, Chrome




56010CM
Mira, Page 333
6" W, 16¼" H
Chrome





4570KZ
Mondrian, Page 201
7" W, 11" H
Buckeye Bronze



4572KZ
Mondrian, Page 201
7" W, 24" H
Buckeye Bronze




52112
Portia, Page 323
3" W, 19" H
Brushed Nickel,
Polished Nickel
 




4912SL
Sabina, Page 227
11½" W, 16¾" H
Silver Leaf



29202SQ
Sawyer, Page 435
9" W, 12" H
Sequoia






59922
Simi, Pages 320, 321
5¼" W, 12½" H
Brushed Nickel, Chrome






4900
Sussex, Pages 273, 276
14" W, 14" H
Brushed Nickel,
English Bronze



51812
Tremont, Page 325
3½" W, 16" H
Brushed Nickel,
Polished Nickel
 



55652
Unity, Page 324
3" W, 15½" H
Brushed Nickel,
Polished Nickel
 



3292VZ
Walden
8" W, 12" H
Victorian Bronze

FLUSH + SEMI-FLUSH MOUNTS PICTORIAL INDEX



67011
Academy, Page 89
5½" Dia., 14½" H
English Nickel,
Oil Rubbed Bronze



67012
Academy, Page 89
10" Dia., 11½" H
English Nickel,
Oil Rubbed Bronze



67013
Academy, Page 89
6½" Dia., 12" H
English Nickel,
Oil Rubbed Bronze



5191CM
Ashley, Page 384
15¼" Dia., 7" H
Chrome



48231R
Beckett, Page 55
14" Dia., 12½" H
Iron Rust



4651
Bolla, Pages 203, 207, 211,
215, 219
19¼" Dia., 14¼" H
Brushed Bronze,
Brushed Nickel, Olde Bronze
T24



4660
Bolla, Pages 207, 211, 215, 219,
386, 388, 389, 390
16¾" Dia., 8" H
Brushed Nickel, Olde Bronze
T24



4669
Bolla, Pages 203, 207, 211,
215, 219
23¼" Dia., 16" H
Brushed Bronze,
Brushed Nickel, Olde Bronze
T24



4631
Brantley, Page 221, 223, 414
17" Dia., 7" H
Brushed Nickel,
Oil Rubbed Bronze



4632
Brantley, Page 221, 223
17" Dia., 10¾" H
Brushed Nickel,
Oil Rubbed Bronze



3612
Cambridge, Pages 297, 298, 299
14½" Dia., 13" H
Burnished Brass,
Olde Bronze, Pewter



3616
Cambridge, Pages 297, 298, 299
16¼" Dia., 7½" H
Burnished Brass,
Olde Bronze, Pewter



4771SL
Carlton, Page 293
24" Dia., 17½" H
Silver Leaf



3521
Charlotte, Pages 182, 183, 184
16" Dia., 13" H
Antique Nickel, Brushed
Caramel, Chrome



3522
Charlotte, Pages 182, 183, 184
20" Dia., 13½" H
Antique Nickel, Brushed
Caramel, Chrome



3031
Clancy, Pages 74, 75, 76, 77
10" Dia., 16¼" H
Aged Zinc, Brushed Nickel,
Buckeye Bronze, Polished Nickel
T24



3231
Colbin, Page 311
12½" Dia., 4¾" H
Aged Zinc, Brushed Nickel,
Oil Rubbed Bronze



3233
Colbin, Page 311
16½" Dia., 5¾" H
Aged Zinc, Brushed Nickel,
Oil Rubbed Bronze



3381
Collier, Pages 115, 117, 119
16½" Dia., 9¼" H
Antique Nickel, Heritage
Brass, Light Oiled Bronze
T24



3382
Collier, Pages 115, 117, 119
22" Dia., 11½" H
Antique Nickel, Heritage
Brass, Light Oiled Bronze
T24



3114
Congress, Page 94
9¼" Dia., 10¼" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3140
Congress, Page 95
8" Dia., 9½" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3143
Congress, Page 95
7" Dia., 11¼" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3144
Congress, Page 95
8¾" Dia., 11" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3146
Congress, Page 95
8" Dia., 9½" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3147
Congress, Page 95
12¼" W, 11¼" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3148
Congress, Page 94
9¾" W, 10½" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3149
Congress, Page 95
7" W, 11¼" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3150
Congress, Page 95
8¾" W, 11" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



3151
Congress, Page 95
6" W, 12" H
Antique Nickel, Chrome,
Oil Rubbed Bronze



4353
Elaine, Pages 254, 255
9¾" Dia., 18¾" H
Light Oiled Bronze,
Polished Antique Nickel



5421
Pages 328, 329, 345
17" Dia., 7" H
Brushed Bronze,
Brushed Nickel, Chrome



5551
Pages 346, 347, 392
15" Dia., 7¾" H
Brushed Bronze,
Brushed Nickel, Chrome



3472
Gentry, Pages 257, 259,
261, 263
9½" Dia., 9¾" H
Heirloom Brass,
Olde Bronze, Pewter,
Polished Nickel



3473
Gentry, Pages 257, 259,
261, 263
11½" Dia., 10½" H
Heirloom Brass,
Olde Bronze, Pewter,
Polished Nickel



3300
Hadley, Page 308
7¾" Dia., 7" H
Antique Nickel, Brushed
Bronze, Chrome,
Oil Rubbed Bronze



3301
Hadley, Page 309
14" Dia., 5½" H
Antique Nickel, Brushed
Bronze, Chrome,
Oil Rubbed Bronze



3302
Hadley, Page 306
12" Dia., 4¾" H
Antique Nickel, Brushed
Bronze, Chrome,
Oil Rubbed Bronze



3304
Hadley, Page 307
20" Dia., 7¾" H
Antique Nickel, Brushed
Bronze, Chrome,
Oil Rubbed Bronze



3308
Hadley, Page 309
7¾" Dia., 4½" H
Antique Nickel, Brushed
Bronze, Chrome,
Oil Rubbed Bronze



4381
Halsey, Page 313
13" Dia., 4½" H
Brushed Nickel,
Buckeye Bronze



4382
Halsey, Page 313
17" Dia., 5¼" H
Brushed Nickel,
Buckeye Bronze



3200
Hampton, Pages 169, 173, 177
15" Dia., 11¾" H
Antique Nickel, Brushed
Bronze, Buckeye Bronze



3201
Hampton, Pages 169, 173, 177
20" Dia., 12" H
Antique Nickel, Brushed
Bronze, Buckeye Bronze



3211
Hampton, Pages 169, 173, 177
26" Dia., 14½" H
Antique Nickel, Brushed
Bronze, Buckeye Bronze



3641
Harper, Page 315
14½" Dia., 10" H
Brushed Nickel, Chrome,
Heritage Brass, Oil Rubbed
Bronze



3643
Harper, Page 314
18" Dia., 10" H
Brushed Nickel, Chrome,
Heritage Brass, Oil Rubbed
Bronze



3701KZ
Harrison, Page 181
15" Dia., 6½" H
Buckeye Bronze



3703KZ
Harrison, Page 181
20" Dia., 10¼" H
Buckeye Bronze



3220
Hathaway, Page 187, 189, 191
16" Dia., 11¾" H
Antique Nickel, Olde Bronze

FLUSH + SEMI-FLUSH MOUNTS PICTORIAL INDEX



3221
Hathaway, Page 187, 189, 191
20¾" Dia., 12¼" H
Antique Nickel, Olde Bronze
T24



3223
Hathaway, Page 187, 189, 191
13" Dia., 4½" H
Antique Nickel, Olde Bronze
T24



3225
Hathaway, Page 187, 189, 191
16" Dia., 5¼" H
Antique Nickel, Olde Bronze
T24



3226
Hathaway, Page 187, 189, 191
21¼" Dia., 6¼" H
Antique Nickel, Olde Bronze
T24



3228
Hathaway, Page 187, 189, 191
7" Dia., 3¼" H
Antique Nickel, Olde Bronze
T24



53241BN
Jules
15" Dia., 8¼" H
Brushed Nickel
T24



3563BV
Lara, Page 161
15" Dia., 8¼" H
Brushed Silver



4483EN
Larchmere, Page 163
18" Dia., 13¾" H
English Nickel



3782
Maxwell, Page 310
13¾" Dia., 5" H
Antique Nickel, Heritage
Brass, Oil Rubbed Bronze



3783
Maxwell, Page 310
19" Dia., 6½" H
Antique Nickel, Heritage
Brass, Oil Rubbed Bronze
T24



3871
Meridian, Pages 195, 364, 365
16" Dia., 12" H
Brushed Nickel, Chrome



4971BN
Midtown, Page 197
18" Dia., 11¼" H
Brushed Nickel



4571KZ
Mondrian, Page 201
16" W, 13½" H
Buckeye Bronze
T24



4102
Plantation, Pages 286, 289, 291,
424, 425, 621, 623
12" Dia., 8" H
Burnished Brass,
Copper Bronze, Pearl Bronze,
Polished Antique Nickel



4881
Plantation, Pages 286, 289, 291,
424, 425, 621, 623
16" Dia., 8¾" H
Burnished Brass,
Copper Bronze, Pearl Bronze,
Polished Antique Nickel



3712FB
Rockford, Page 301
14½" Dia., 12½" H
Forum Bronze



4911SL
Sabina, Page 227
15" Dia., 7" H
Silver Leaf



29201SQ
Sawyer, Page 435
9" Dia., 4½" H
Sequoia
T24



29203SQ
Sawyer, Page 435
15" Dia., 4¾" H
Sequoia
T24



4791
Sussex, Page 274, 277
16" Dia., 15" H
Brushed Nickel,
English Bronze



4021AN
Truman, Page 225
16" Dia., 12" H
Antique Nickel



3291VZ
Walden
13" Dia., 7" H
Victorian Bronze



3971
Weston, Page 312
13½" Dia., 5" H
Buckeye Bronze,
Brushed Nickel



3972
Weston, Page 312
15" Dia., 5¾" H
Buckeye Bronze,
Brushed Nickel



3441
Zelda, Pages 156, 157
14¾" Dia., 12½" H
Polished Nickel,
Vintage Brass



67071
Academy, Page 88
5½" Dia., 13¼" H
47¼" Max. H
English Nickel,
Oil Rubbed Bronze



67072
Academy, Page 88
10" Dia., 10½" H
44½" Max. H
English Nickel,
Oil Rubbed Bronze



67073
Academy, Page 88
6½" Dia., 11" H
45" Max. H
English Nickel,
Oil Rubbed Bronze



3122
Amelia, Pages 81, 83
11½" Dia., 9¾" H
42¾" Max. H
Aged Zinc,
Buckeye Bronze,
Polished Antique Nickel,
Polished Nickel,
Polished White



3123
Amelia, Page 85
11½" Dia., 9" H
42" Max. H
Buckeye Bronze,
Chrome,
Polished Antique
Nickel



3124
Amelia, Page 84
12¾" Dia., 13¾" H
46¾" Max. H
Buckeye Bronze,
Chrome,
Polished Antique
Nickel



3126
Amelia, Pages 81, 82
12¾" Dia., 14" H
47" Max. H
Aged Zinc,
Buckeye Bronze,
Polished Antique Nickel,
Polished White



3127
Amelia, Page 84
11½" Dia., 9¾" H
42¾" Max. H
Buckeye Bronze,
Chrome,
Polished Antique
Nickel



2302
Aria, Pages 485, 487
5¼" Dia., 15¾" H
48" Max. H
Black,
Buckeye Bronze



3027
Astrid, Pages 126, 127
12" W, 10½" H
43¾" Max. H
Deluxe Gold,
Metallic Matte Bronze



3277
Atrium, Pages 124
18¾" W, 19" H
58½" Max. H
Bronze



1112
Atwell, Pages 438, 439
14½" Dia., 11" H
44" Max. H
Aged Zinc,
Oil Rubbed Bronze



3604
Barstow, Page 79
16¼" Dia., 12" H
45" Max. H
Buckeye Bronze,
Galvanized



2862OZ
Belden Place
Page 569
10" Dia., 16½" H
49" Max. H
Oil Rubbed Bronze



5357
Bennett
Pages 366, 367
5¼" Dia., 9" H
47¼" Max. H
Polished Antique Nickel,
Polished Nickel



3797
Blakely, Pages 165, 167
12" Dia., 16" H
60½" Max. H
Brushed Nickel,
Buckeye Bronze



4661
Bolla, Pages 205,
209, 213, 217
15½" Dia., 8¼" H
48" Max. H
Brushed Nickel,
Olde Bronze



4667
Bolla, Page 203,
205, 209, 213, 217
15½" Dia., 8¼" H
48" Max. H
Brushed Bronze,
Brushed Nickel,
Olde Bronze



4637
Brantley, Pages 221, 223
4¾" Dia., 9" H
41¼" Max. H
Brushed Nickel,
Oil Rubbed Bronze



2792OZ
Burke, Pages 538, 539
9" W, 13" H
54½" Max. H
Oil Rubbed Bronze



29707
Carson
Pages 441, 443
10" Dia., 10½" H
46" Max. H
Vintage Iron,
Weathered Zinc



2492KZ
Briggs, Page 571
8¾" Dia., 18" H
50¾" Max. H
Buckeye Bronze



3397
Cartwright, Pages 61,
62, 63
11½" Dia., 15" H
47" Max. H
Galvanized, Polished
Antique Nickel,
Rustic Brass



3394
Cartwright, Pages 61,
62, 63
15¼" Dia., 19¾" H
47" Max. H
Galvanized, Polished
Antique Nickel,
Rustic Brass



4017
Casa, Pages 267, 269
5½" Dia., 13" H
45" Max. H
Olde Black



3031
Clancy, Pages 74,
75, 76, 77
10" Dia., 15½" H
48¼" Max. H
Aged Zinc,
Brushed Nickel,
Buckeye Bronze,
Polished Nickel



2922
Colfax, Pages 502, 503
9½" W, 18¾" H
60¼" Max. H
Bronze, Polished
Stainless Steel



3110
Congress, Page 99
9¼" Dia., 8¼" H
40¾" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



3128
Congress, Page 98
7" Dia., 9¼" H
41¾" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



3129
Congress, Page 98
8¾" Dia., 9" H
41½" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



3130
Congress, Page 97
8" Dia., 7" H
39½" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



3133
Congress, Page 97
7" Dia., 9¼" H
41¾" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



3134
Congress, Page 97
8¾" Dia., 9" H
41½" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



3136
Congress, Page 98
8" Dia., 7" H
39½" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



3137
Congress, Page 98
12" Dia., 9¾" H
42¼" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



3138
Congress, Page 99
9¾" Dia., 8½" H
41" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze





3139
Congress, Page 98
6" Dia., 10" H
42½" Max. H
Antique Nickel,
Chrome,
Oil Rubbed Bronze



32671N
Denton, Page 57
5¼" Dia., 10" H
42" Max. H
Industrial Iron



2192
Dorian, Pages 481, 483
6" W, 18¼" H
Bronze, Titanium
 



3054
Elliott, Page 78
13" Dia., 6¾" H
46" Max. H
Antique Nickel,
Greystone,
Regency Bronze



3097
Elroy, Page 80
10" Dia., 10" H
43" Max. H
Aged Zinc,
Brushed Nickel,
Heritage Brass,
Olde Bronze,
Polished Nickel




3684
Finley, Page 112
10" Dia., 13½" H
58" Max. H
Brushed Nickel,
Chrome,
Oil Rubbed Bronze



3687
Finley, Page 112
6" Dia., 8¾" H
53¼" Max. H
Brushed Nickel,
Chrome,
Oil Rubbed Bronze



4497PL
Fleming, Page 239
8" W, 14½" H
47¼" Max. H
Polished
Antique Nickel



4834
Fletcher, Page 87
13½" Dia., 14½" H
49¼" Max. H
Aged Zinc with Heritage
Brass, Aged Zinc
with Polished Nickel,
Polished Nickel



3927
Fulham, Pages 144, 145
7¾" W, 9" H
41¾" Max. H
Buckeye Bronze,
Polished Antique Nickel



3337
Fulton, Pages 134, 138
10" W, 8¾" H
53½" Max. H
Aged Zinc, Bronze



3351
Fulton, Pages 133, 137
10" W, 12½" H
51¼" Max. H
Aged Zinc, Bronze



4937
Gatsby, Pages 104, 105
4½" Dia., 8¼" H
41½" Max. H
Heritage Brass,
Polished Antique Nickel



3207
Hampton, Pages 174, 178
7" Dia., 11¾" H
44" Max. H
Antique Nickel,
Brushed Bronze,
Buckeye Bronze



3567BV
Lara, Page 161
8¼" Dia., 12¼" H
45" Max. H
Brushed Silver



3997
Latitude, Pages 198, 199
8" W, 16½" H
55" Max. H
Brushed Nickel,
Oil Rubbed Bronze





3587
Margeaux, Pages 153, 155
3½" Dia., 14¼" H
47¼" Max. H
Polished Nickel,
Vintage Brass



3494
Marlowe, Page 113
10¾" Dia., 16¼" H
Antique Nickel,
Oil Rubbed Bronze



3497
Marlowe, Page 113
8" Dia., 12¾" H
Antique Nickel,
Oil Rubbed Bronze



3877BN
Meridian, Page 195
7½" Dia., 4½" H
36¾" Max. H
Brushed Nickel



3777
Middleton, Pages 65, 67
8" Dia., 12¾" H
45½" Max. H
Graphite Bronze,
Polished Nickel



4577KZ
Mondrian, Page 201
7" W, 11" H
43¾" Max. H
Buckeye Bronze



4744
Odeon, Page 122
15" Dia., 18" H
54¾" Max. H
Brushed Nickel,
Oil Rubbed Bronze



2382OZ
Perry, Page 550
5¼" Dia., 16" H
48½" Max. H
Oil Rubbed Bronze



5317
Plantation, Pages 285,
288, 291
5" Dia., 8¼" H
40¾" Max. H
Burnished Brass,
Polished Antique Nickel,
Pearl Bronze



4247
Plymouth, Pages 280, 283
6½" Dia., 10½" H
43" Max. H
Olde Bronze,
Polished Antique
Nickel



3254
Pullman, Page 73
7¼" Dia., 11" H
44" Max. H
Brushed Nickel,
Chrome,
Oil Rubbed Bronze



3257
Pullman, Page 73
10" Dia., 14½" H
47½" Max. H
Brushed Nickel,
Chrome,
Oil Rubbed Bronze



4813
 Quentin, Pages 129, 131
 8½" W, 14" H
 45½" Max. H
 Aged Zinc,
 Buckeye Bronze



63307
 Refinery, Page 111
 7¾" Dia., 12" H
 56¾" Max. H
 Black, Brushed Nickel,
 Chrome



4367
 Rigby, Pages 107, 108, 109
 10" Dia., 4¼" H
 37¼" Max. H
 Aged Zinc,
 Buckeye Bronze,
 Polished Nickel



1322
 Shelter, Page 489,
 491, 493
 6¼" W, 21¾" H
 54¼" Max. H
 Black, Buckeye Bronze,
 Hematite
 ♻️ 🌙 124



1328BK
 Shelter, Page 489
 8¼" W, 24½" H
 57" Max. H
 Black
 ♻️ 🌙 124



3407
 Somerset, Page 123
 11½" Dia., 17" H
 49¾" Max. H
 Brushed Nickel,
 Buckeye Bronze,
 Heritage Brass



4717RB
 Tahoe
 7" W, 6¾" H
 39½" Max. H
 Regency Bronze



3574DZ
 Theory, Page 125
 15¼" W, 14¾" H
 49¼" Max. H
 Aged Zinc



1192
 Troyer, Page 436
 10" Dia., 7½" H
 40" Max. H
 Aged Zinc, Black,
 Oil Rubbed Bronze
 ⚠️



4027AN
 Truman, Page 225
 5¼" Dia., 8¼" H
 40¼" Max. H
 Antique Nickel



2102
 Walker, Pages 541, 543
 11½" W, 17¼" H
 50" Max. H
 Black,
 Buckeye Bronze
 ♻️



3447
 Zelda, Pages 146, 147
 4¾" Dia., 12½" H
 44¾" Max. H
 Polished Nickel,
 Vintage Brass



83669AN
33¼" L, 4¼" W, 1¼" H
linear ceiling adapter



83669BN
33¼" L, 4¼" W, 1¼" H
linear ceiling adapter



83667AN
14½" Dia., 1¼" H
round ceiling adapter



83667BN
14½" Dia., 1¼" H
round ceiling adapter



83669CM
33¼" L, 4¼" W, 1¼" H
linear ceiling adapter



83669OZ
33¼" L, 4¼" W, 1¼" H
linear ceiling adapter



83667CM
14½" Dia., 1¼" H
round ceiling adapter



83667OZ
14½" Dia., 1¼" H
round ceiling adapter

make a statement

with multiples by using round and linear ceiling adapters with your favorite pendants



3685
Finley
40" W, 58½" H
Brushed Nickel,
Chrome,
Oil Rubbed Bronze



3689
Finley
36" W, 53½" H
Brushed Nickel,
Chrome,
Oil Rubbed Bronze



3686
Finley
21" Dia., 58½" H
Brushed Nickel,
Chrome,
Oil Rubbed Bronze



3688
Finley
17" Dia., 53½" H
Brushed Nickel,
Chrome,
Oil Rubbed Bronze

ITEM	BULBS	DEPTH	CANOPY	WIRE	STEMS INCLUDED
3685 BN, 3685 CM, 3685 OZ	3-100w Med.	10"	4¼" W, 33¼" L	30'	3-6", 9-12"
3686 BN, 3686 CM, 3686 OZ	3-100w Med.		14½" Dia.	30'	3-6", 9-12"
3688 BN, 3688 CM, 3688 OZ	3-100w Med.		14½" Dia.	30'	3-6", 9-12"
3689 BN, 3689 CM, 3689 OZ	3-100w Med.	10"	4¼" W, 33¼" L	30'	3-6", 9-12"



ABBIE
Page 405
Brushed Caramel



ABBIE
Page 406
Brushed Nickel



ABBIE
Page 407
Chrome



ACCLAIM
Page 322
Brushed Nickel



ACCLAIM
Page 322
Polished Nickel



AINSLEY
Page 381
Brushed Nickel



AINSLEY
Page 380
Buckeye Bronze



AINSLEY
Page 382
Polished Nickel



ALICE
Page 393
Antique Nickel



ALICE
Page 392
Brushed Bronze



ASHLEY
Page 384
Chrome



AVON
Page 352
Brushed Nickel



AVON
Page 351
Chrome



AVON
Page 350
Chrome



AVON
Page 349
Buckeye Bronze



BALDWIN
Page 394
Antique Nickel



BALDWIN
Page 395
Polished Nickel



BENNETT
Page 366
Polished Antique Nickel



BENNETT
Page 367
Polished Nickel



BLYTHE
Page 412
Antique Nickel



BLYTHE
Page 413
Polished Nickel



BOLLA
Page 386
Brushed Nickel



BOLLA
Page 387
Brushed Nickel



BOLLA
Page 390
Olde Bronze



BOLLA
Page 388
Olde Bronze



BOLLA
Page 389
Olde Bronze



BOYER
Page 368
Oil Rubbed Bronze



BOYER
Page 369
Polished Nickel



BRANTLEY
Page 414
Brushed Nickel



BRANTLEY
Page 415
Olde Bronze



BROOKE
Page 418
Antique Nickel



BROOKE
Page 417
Olde Bronze



BROOKE
Page 416
Silver Leaf



CASA
Page 423
Olde Black



CASA
Page 422
Olde Black



CHLOE
Page 338
Brushed Nickel



CLANCY
Page 373
Brushed Nickel



COLETTE
Page 402
Brushed Nickel



COLETTE
Page 403
Chrome



COLETTE
Page 404
Oil Rubbed Bronze



CONGRESS
Page 375
Antique Nickel



CONGRESS
Page 375
Chrome



CONGRESS
Page 375
Oil Rubbed Bronze



CONGRESS
Page 374
Antique Nickel



CONGRESS
Page 374
Chrome



CONGRESS
Page 374
Oil Rubbed Bronze



CONGRESS
Page 374
Antique Nickel



CONGRESS
Page 374
Chrome



CONGRESS
Page 374
Oil Rubbed Bronze



CONGRESS
Page 374
Antique Nickel



CONGRESS
Page 374
Chrome



CONGRESS
Page 374
Oil Rubbed Bronze



CONGRESS
Page 374
Antique Nickel



CONGRESS
Page 374
Chrome



CONGRESS
Page 374
Oil Rubbed Bronze



CONGRESS
Page 374
Antique Nickel



CONGRESS
Page 374
Chrome



CONGRESS
Page 374
Oil Rubbed Bronze



CONGRESS
Page 374
Antique Nickel



CONGRESS
Page 374
Chrome



CONGRESS
Page 374
Oil Rubbed Bronze



CONGRESS
Page 374
Antique Nickel



CONGRESS
Page 374
Chrome



CONGRESS
Page 374
Oil Rubbed Bronze



CONGRESS
Page 377
Antique Nickel



CONGRESS
Page 377
Chrome



CONGRESS
Page 377
Oil Rubbed Bronze



DAPHNE
Page 336
Brushed Nickel
♻️ T24 ♿



DAPHNE
Page 337
Brushed Bronze
♿



DAPHNE
Page 335
Chrome
♻️ T24 ♿



DARBY
Page 399
Brushed Caramel



DARBY
Page 397
Brushed Nickel



DARBY
Page 398
Polished Nickel



DARIA
Page 332
Chrome



FAIRLANE
Page 326
Brushed Nickel
♻️ T24 ♿



FAIRLANE
Page 326
Chrome
♻️ T24 ♿



FAYE
Page 383
Chrome



FRANCOISE
Page 421
Burnished Brass



FRANCOISE
Page 420
Polished Antique Nickel



JACKSON
Page 372
Brushed Nickel



JACKSON
Page 371
Buckeye Bronze



JACKSON
Page 370
Polished Nickel



JOSIE
Page 385
Brushed Nickel



KARLIE
Page 359
Brushed Nickel



KARLIE
Page 358
Chrome



KYRA
Page 357
Brushed Nickel



KYRA
Page 356
Polished Nickel



LANZA
Page 343
Antique Nickel
♻️



LANZA
Page 345
Brushed Bronze
♻️



LANZA
Page 344
Buckeye Bronze
♻️



LATITUDE
Page 340
Brushed Nickel
124



LATITUDE
Page 339
Chrome
124



LATITUDE
Page 341
Oil Rubbed Bronze
124



LAUREL
Page 360
Brushed Nickel



LAUREL
Page 361
Polished Nickel



MERIDIAN
Page 365
Brushed Nickel



MERIDIAN
Page 334
Chrome



MILA
Page 331
Brushed Nickel



MILA
Page 330
Chrome



MILEY
Page 355
Brushed Nickel



MILEY
Page 354
Chrome



MIRA
Page 333
Chrome



PINNACLE
Page 362
Antique Nickel



PINNACLE
Page 363
Chrome



PLANTATION
Page 425
Burnished Brass



PLANTATION
Page 424
Polished Antique Nickel



PORTIA
Page 323
Brushed Nickel
124



PORTIA
Page 323
Polished Nickel
124



REESE
Page 419
Antique Nickel



RIGBY
Page 378
Antique Nickel



RIGBY
Page 379
Polished Nickel



SADIE
Page 396
Brushed Nickel




SAN SIMEON
Page 426
Silver Leaf



SHELLY
Page 410
Brushed Nickel



SHELLY
Page 411
Chrome



SIMI
Page 320
Brushed Nickel



SIMI
Page 321
Chrome



TAYLOR
Page 346
Brushed Nickel



TAYLOR
Page 347
Chrome



TAYLOR
Page 348
Buckeye Bronze



TESSA
Page 353
Chrome



THISTLEDOWN
Page 401
Brushed Nickel



THISTLEDOWN
Page 400
Polished Nickel



TREMONT
Page 325
Brushed Nickel



TREMONT
Page 325
Polished Nickel



UNITY
Page 324
Brushed Nickel



UNITY
Page 324
Polished Nickel



VERVE
Page 342
Chrome



WINTON
Page 328
Brushed Nickel



WINTON
Page 329
Chrome



YORKTOWN
Page 408
Antique Nickel



YORKTOWN
Page 409
Brushed Bronze



ADAIR
Pages 576-577
Aged Zinc



ALFORD PLACE
Pages 596-597
Oil Rubbed Bronze



ANCHORAGE
Pages 578-579
Aged Zinc



ANCHORAGE
Pages 580-581
Light Oiled Bronze



ARIA
Pages 484-485
Black



ARIA
Pages 486-487
Buckeye Bronze



ATLANTIS
Pages 476-477
Bronze



ATLANTIS
Pages 472-473
Satin Black



ATLANTIS
Page 478
Satin White



ATLANTIS
Pages 474-475
Titanium



ATWELL
Page 439
Aged Zinc



ATWELL
Page 438
Oil Rubbed Bronze



AUGUSTA
Pages 658-659
Copper Bronze



BARRINGTON
Page 627
Victorian Bronze



BECKETT
Page 433
Iron Rust



BELDEN PLACE
Page 569
Oil Rubbed Bronze



BINGHAM
Pages 584-585
Greystone



BINGHAM
Pages 586-587
Sienna



BOLLA
Pages 610-611
Olde Bronze



BOLLA
Pages 612-613
Olde Bronze



BRIGGS
Page 571
Buckeye Bronze



BROMLEY
Page 604-605
Museum Black



BROMLEY
Pages 606-607
Oil Rubbed Bronze



BRYNMAR
Page 619
Regency Bronze



BURKE
Page 538
Oil Rubbed Bronze

OUTDOOR PICTORIAL INDEX



BURKE
Page 539
Oil Rubbed Bronze



BURTON
Page 544
Black



CALISTOGA
Page 563
Spanish Bronze



CAMELOT
Page 644
Black



CAPE COD
Page 564-565
Aged Zinc



CAPE COD
Page 566-567
Sienna Bronze



CARSON
Pages 442-443
Vintage Iron



CARSON
Pages 440-441
Weathered Zinc



CASA
Pages 616-617
Olde Black



CASA
Pages 614-615
Olde Black



CASCADE
Page 470
Bronze



CASCADE
Page 470
Satin Black



CASCADE
Page 470
Titanium



CASTELLE
Page 520
Black



CASTELLE
Page 521
Bronze



CHERRY CREEK
Pages 514-515
Oil Rubbed Bronze



CHERRY CREEK
Pages 516-517
Vintage Black



CLIFTON PARK
Pages 660-661
Copper Bronze



COLFAX
Page 503
Bronze



COLFAX
Page 502
Polished Stainless Steel



DORIAN
Pages 482-483
Bronze



DORIAN
Pages 480-481
Titanium



EDGEWATER
Pages 646-647
Black



EDGEWATER
Pages 648-649
Oil Rubbed Bronze



ENZO
Pages 608-609
Oil Rubbed Bronze



FREEPORT
Page 558
Black
☼ 124



FREEPORT
Page 556
Classic White
☼ 124



FREEPORT
Page 557
Oil Rubbed Bronze
☼ 124



FREEPORT
Page 559
Olde Penny
☼ 124



GLACIER
Page 447
Bronze
☼ 124 ♿



GLACIER
Page 446
Titanium
☼ 124 ♿



HADLEY
Page 528
Buckeye Bronze



HARBOR
Pages 512-513
Anchor Bronze
☼ 124



HARBOR
Pages 510-511
Satin Black
☼ 124



HARBOR
Pages 508-509
Titanium
☼ 124



HORIZON
Pages 494-495
Black
☼ 124 ♿



HORIZON
Pages 494-495
Buckeye Bronze
☼ 124 ♿



HUDSON
Page 529
Oil Rubbed Bronze



KEY WEST
Pages 650-651
Regency Bronze



KORE
Pages 468-469
Bronze
☼ ♿ ♿



KORE
Pages 468-469
Titanium
☼ ♿ ♿



KUBE
Page 479
Bronze
☼ ♿ 124 ♿



KUBE
Page 479
Satin Black
☼ ♿ 124 ♿



KUBE
Page 479
Satin White
☼ ♿ 124 ♿



KUBE
Page 479
Titanium
☼ ♿ 124 ♿



LEDGEWOOD
Pages 518-519
Museum Bronze



LEX
Page 460
Bronze
☼ 124



LEX
Page 460
Stainless Steel
☼ 124



LINCOLN
Pages 594-595
Oil Rubbed Bronze



LUCERNE
Pages 662-663
Copper Bronze



LUNA
Pages 462-467
Bronze



LUNA
Pages 462-467
Satin Black



LUNA
Pages 462-467
Titanium



LUNA
Page 467
Satin White



MANHATTAN
Pages 506-507
Oil Rubbed Bronze



MANHATTAN
Pages 504-505
Oil Rubbed Bronze



MANOR HOUSE
Pages 642-643
Black



MARINA
Page 554
Bronze



MARINA
Page 555
Hematite



MIST
Page 451
Bronze



MIST
Page 452
Satin Black



MIST
Page 450
Titanium



MONDRIAN
Page 533
Buckeye Bronze



MONTAUK
Page 589
Sienna



MONTICELLO
Pages 656-657
Copper Bronze



NANTUCKET
Page 588
Aged Brass



NEW CASTLE
Pages 560-561
Black



NEWPORT
Page 548
Aged Zinc



OXFORD
Page 636-637
Midnight Bronze



PERRY
Page 550
Oil Rubbed Bronze



PLANTATION
Pages 622-623
Copper Bronze



PLANTATION
Pages 620-621
Pearl Bronze



PLAZA
Page 453
Bronze



PLAZA
Page 453
Titanium



PORTER
Pages 572-573
Aged Zinc



QUINCY
Page 531
Aged Zinc
♻️ 174



QUINCY
Page 530
Oil Rubbed Bronze
♻️ 174



RALEY
Pages 630-631
Museum Black
♻️



RALEY
Pages 628-629
Oil Rubbed Bronze
♻️



RANDOLPH
Pages 524-525
Black



REEF
Page 553
Hematite
♻️ 174



REEF
Page 552
Victorian Bronze
♻️ 174



REGAL
Page 645
Black Granite



REVERE
Pages 590-591
Sienna



RILEY
Page 532
Oil Rubbed Bronze
♻️ 174



SAN CLEMENTE
Pages 652-653
Copper Bronze



SAN CLEMENTE
Pages 654-655
Museum Black



SATURN
Pages 498-499
Metro Bronze
♻️ 174



SATURN
Pages 496-497
Satin Black



SATURN
Pages 500-501
Stainless Steel
♻️ 174



SAWYER
Pages 434-435
Sequoia
♻️ ♿



SAYBROOK
Page 568
Oil Rubbed Bronze



SEDGWICK
Page 593
Sienna



SENATOR
Page 641
Black



SHELTER
Pages 488-489
Black
♻️ 🌙 174 ♿



SHELTER
Pages 490-491
Buckeye Bronze
♻️ 🌙 174 ♿



SHELTER
Pages 492-493
Hematite
♻️ 🌙 174 ♿



SORRENTO
Page 618
Aged Iron



SULLIVAN
Page 534
Black
♻️ 174



SULLIVAN
Page 535
Hematite
♻️ 174



SULLIVAN
Page 536
Oil Rubbed Bronze
☼ 174



SURF
Page 458
Bronze
☼ 174



SURF
Page 456
Satin Black
☼ 174



SURF
Page 459
Stainless Steel
☼ 174



SURF
Page 457
Titanium
☼ 174



SUTCLIFFE
Page 547
Aged Zinc
☼



SUTCLIFFE
Page 546
Oil Rubbed Bronze
☼



TAHOE
Pages 526-527
Regency Bronze



TATUM
Page 570
Oil Rubbed Bronze



THATCHER
Page 545
Antique Copper



THEO
Page 537
Oil Rubbed Bronze
☼ ☾



TITAN
Page 471
Buckeye Bronze
☼ 174



TITAN
Page 471
Titanium
☼ 174



TRAFALGAR
Page 638
Mocha



TRAFALGAR
Page 639
Museum Black



TRELLIS
Pages 598-600
Aged Zinc
☼



TRELLIS
Pages 601-603
Regency Bronze
☼



TROYER
Pages 436-437
Aged Zinc
☼



TROYER
Pages 436-437
Oil Rubbed Bronze
☼



TUCKER
Page 522
Museum Black
☼ 174



TUCKER
Page 523
Oil Rubbed Bronze
☼ 174



VAPOR
Page 449
Bronze
♿



VAPOR
Page 448
Titanium
♿



VISTA
Page 455
Bronze
☼ 174 ♿



VISTA
Page 455
Titanium
☼ 174 ♿



VUE
Page 454
Bronze



VUE
Page 454
Titanium



WABASH
Page 640
Museum Black



WALKER
Pages 542-543
Black



WALKER
Pages 540-541
Buckeye Bronze



WESTPORT
Page 549
Aged Zinc



WESTPORT
Page 549
Buckeye Bronze



WESTWINDS
Pages 624-625
Sienna



WINDSOR
Pages 632-633
Black



WINDSOR
Pages 634-635
River Rock



YORK
Pages 582-583
Black

OUTDOOR FLUSH MOUNTS PICTORIAL INDEX



2633OB
Bolla, Page 613
16¾" Dia., 8" H
Olde Bronze
T24



2643OB
Bolla, Page 611
16¾" Dia., 8" H
Olde Bronze



2203
Cape Cod, Pages 565, 567
7" Dia., 9¾" H
Aged Zinc, Sienna Bronze
T24



1273
Cherry Creek, Pages 515, 517
12" W, 7¼" H
Oil Rubbed Bronze,
Vintage Black
T24



2429CB
Clifton Park, Page 661
10¾" W, 6¾" H
Copper Bronze



1683
Edgewater, Pages 647, 649
13" W, 6¾" H
Black, Oil Rubbed Bronze



2573
Harbor, Pages 509, 511, 513
12¼" W, 7" H
Anchor Bronze, Satin Black,
Titanium
T24



2903RB
Key West, Page 651
15" Dia., 8¼" H
Regency Bronze



1765
Kube, Page 479
6" W, 6" H
Bronze, Satin Black,
Satin White, Titanium
T24



1665
Luna, Page 465
8" W, 3¼" H
Bronze, Satin Black,
Titanium
T24



2413
Marina, Pages 554, 555
10¼" Dia., 5" H
Bronze, Hematite



1243MN
Oxford, Page 637
16¼" Dia., 7½" H
Midnight Bronze



2123PZ
Plantation, Page 621
16" Dia., 12" H
Pearl Bronze



2128PZ
Plantation, Page 621
12" Dia., 8" H
Pearl Bronze



4102
Plantation, Pages 286, 289, 291,
424, 425, 621, 623
12" Dia., 8" H
Burnished Brass,
Copper Bronze, Pearl Bronze,
Polished Antique Nickel



4881
Plantation, Pages 286, 289, 291,
424, 425, 621, 623
16" Dia., 8¾" H
Burnished Brass,
Copper Bronze, Pearl Bronze,
Polished Antique Nickel



1713BG
Regal, Page 645
11¾" Dia., 9¼" H
Black Granite



2443
San Clemente, Page 653, 655
13¾" W, 9" H
Copper Bronze,
Museum Black



29201SQ
Sawyer, Page 435
9" Dia., 4½" H
Sequoia



29203SQ
Sawyer, Page 435
15" Dia., 4¾" H
Sequoia



2243RB
Tahoe, Page 527
9½" W, 6" H
Regency Bronze


LIGHTING MADE SIMPLE

Hinkley is here to be your go-to guide for lighting tips, trends and technical how-tos. Our *Lighting Made Simple™* suite of materials provides the valuable knowledge you need to assist in sizing and selecting a home full of fixtures. Head to hinkleylighting.com for the following resources that will help you find lighting you will love!



MAGAZINES

Filled with inspiring photography, articles, tips, trends and technical how-tos, Hinkley's Lighting Made Simple publications are the ultimate resources to assist you in selecting lighting for your home!



VIDEO WORKSHOPS

Check out our video workshops for a firsthand view of Hinkley's decorative lighting tips and tricks! Get ready to learn about:

- SIZING AND SELECTING A CHANDELIER
- FINDING PERFECT OUTDOOR LANTERNS
- LIGHTING OVER A KITCHEN ISLAND
- LIGHTING THE HALLWAY AND STAIRCASE
- 3 TIPS TO FIND LIGHTING YOU WILL LOVE




LIGHTING 101 INTERACTIVE SHOWHOUSES

Visit hinkleylighting.com to view Lighting 101 and Landscape Lighting 101, the interactive show houses that will walk you through sizing, selecting and installing a home full of interior fixtures, as well as planning and placing landscape lighting that will accent your exterior property.



“Lighting is an expression of the home’s character—the atmosphere one wants it to evoke. The right lighting in an entry sets the tone for the entire experience of the home.”



KELLY DECK
KELLY DECK DESIGN
VANCOUVER, BC

ABOVE: THE ASCHER COLLECTION | 4752BC, PAGE 158
OPPOSITE PAGE: THE EUCLID COLLECTION | 3469SB, PAGE 151

INTERIOR COLLECTIONS



ALISTER	240	CLANCY	074	FULHAM	144	MARGEAUX	152	RUTHERFORD	244
AMELIA	081	CLARENDON	236	FULTON	132	MARLOWE	113	SABINA	226
ASCHER	158	COLBIN	311	GATSBY	104	MAXWELL	310	SOMERSET	123
ASTRID	126	COLLIER	114	GENTRY	256	MERCER	303	SORRENTO	265
ATRIUM	124	CONGRESS	091	HADLEY	306	MERIDIAN	193	SURREY	232
AVENUE	305	CORDILLERA	264	HALSEY	313	MIDDLETON	064	SUSSEX	272
BARSTOW	079	DAKOTA	068	HAMPTON	168	MIDTOWN	196	TERRA	146
BECKETT	054	DENTON	056	HARPER	314	MONDRIAN	200	THEORY	125
BLAKELY	164	ELAINE	254	HARRISON	180	MORGAN	228	TRUMAN	224
BOLLA	202	ELEANOR	246	HATHAWAY	186	ODEON	122	WAVERLY	234
BOYER	140	ELLIOTT	078	HEYWOOD	052	PLANTATION	284	WESTON	312
BRANTLEY	220	ELROY	080	HOWELL	120	PLYMOUTH	278	WEXLEY	252
CAMBRIDGE	296	EUCLID	148	LANZA	304	PULLMAN	073	WYATT	058
CARLTON	292	FENMORE	072	LARA	160	QUENTIN	128	ZELDA	156
CARTWRIGHT	060	FINLEY	112	LARCHMERE	162	REFINERY	110		
CASA	266	FLEMING	239	LATITUDE	198	RIGBY	107		
CHARLOTTE	182	FLETCHER	086	MARCELLINA	294	ROCKFORD	300		

LAYERING EFFECT

Kitchens are the activity hub of the home. Since this multi-tasking mecca is both a social spot and a workspace, a mixture of ambient and task lighting is a must. The key is to balance multiple light sources so the space is as inviting as it is functional.

Chandeliers, pendants, flush and semi-flush mounts add a dose of overhead décor—but remember to hang fixtures accordingly to avoid obstructing your line of sight. Properly placing sconces and under cabinet lighting will allow for the added ambient layering you need to transition your setting from the daytime dash to evening entertaining.

“It takes the combination of lighting—ambient, task, and overhead—working together to make the room both decorative and completely functional.”



ERIKA HOLLINSHEAD WARD
ERIKA WARD INTERIORS | ATLANTA, GA







CELEBRATE SMALL SPACES

Small spaces don't demand that style has to be sacrificed. Whether you choose to live in a smaller house or one with a larger footprint, every home has petite rooms that can be made into something special. In fact, constraint often encourages creativity! Since natural light is sometimes scarce in these compact areas, consider lighting solutions that offer a one-two punch like pendants, flush mounts and sconces. With an amazing array of sizes, styles and finishes to choose from, you acquire critical task illumination without being forced to surrender style in these snug spots!

"Clients sometimes feel like the lighting should be small and subtle or even recessed to match the scale of the room. However, boring lighting makes a space forgettable. I like to use statement lights to define the space, even in tiny or low-ceilinged rooms."



BECKI OWENS
BECKIOWENS.COM
SOUTHERN CALIFORNIA

LEFT: THE FLETCHER COLLECTION | 4834DZ, PAGE 87



boho jungle

RESTORE AND RENEW BY BLENDING INTERIOR COMFORTS WITH OUTDOOR INFLUENCE

- + hand-crafted furniture and artisanal textiles
- + lighting with wooden elements and rich metal finishes
- + exotic foliage and sunset hues
- + globally-sourced accessories with woven textures and tassels

ABOVE: THE DENTON COLLECTION | 3260IN, PAGE 57

HEYWOOD™

FINISH WEATHERED ZINC
WITH COTTAGE WHITEWASH

Heywood's dynamic mix is the perfect blend of rustic and cosmopolitan flair. Elegant globe style vintage bulbs are a chic focal point, while the textured, layered design of wood, metal and rope creates visual excitement.



4279 WZ
30½" DIA., 36½" H



4278 WZ
30½" DIA., 28" H



4275 WZ
24¾" DIA., 24½" H



4276 WZ
24¾" DIA., 31" H



4274 WZ
19" DIA., 25" H



4273 WZ
19" DIA., 19¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
4273 WZ	3-100w Med.*	5¼" Dia.	6', 5'
4274 WZ	3-100w Med.*	5¼" Dia.	6', 5'
4275 WZ	5-100w Med.*	5¼" Dia.	6', 5'
4276 WZ	5-100w Med.*	5¼" Dia.	6', 5'
4278 WZ	7-100w Med.*	5¼" Dia.	12', 10'
4279 WZ	7-100w Med.*	5¼" Dia.	12', 10'

*60w G-45 bulbs included.

BECKETT™

FINISH IRON RUST
WITH AGED CHESTNUT

Beckett's combination of vintage industrial and rustic elements imparts a design that resonates with texture and depth. A sturdy steel mesh shade interspersed with solid wood uprights is captured in an open frame. A subtly designed center down light is surrounded by minimalist arms with visible sockets to customize with the bulbs of your choice.

Beckett Open Air, page 433




4826 IR
30" DIA., 27¼" H
59½" MAX. H*



4823 IR
14" DIA., 12½" H



4825 IR
42" W, 24" H



4824 IR
22¼" DIA., 23" H
55¼" MAX. H*



4820 IR
8" W, 10¼" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TTO	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
4820 IR	1-100w Med.		5"	5¼"	8" W, 10¼" H Back Plate		
4823 IR	3-100w Med.				5¼" Dia. Canopy		
4824 IR	3-100w Med., 1-35w GU-10**				5¼" Dia. Canopy	10'	1-6", 2-12"
4825 IR	4-100w Med., 1-35w GU-10**	12"			4¾" W, 6¾" L Canopy	12', 10'	
4826 IR	5-100w Med., 1-35w GU-10**				5¼" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6033 IN. **GU-10 bulb for downlight included. Ideal for vintage filament bulbs (not included).

DENTON™

FINISH INDUSTRIAL IRON
WITH VINTAGE WALNUT
GLASS CLEAR

Vintage warmth meets modern minimalism in the Denton collection. Offering a range of refined designs to choose from, Denton integrates an Industrial Iron finish with rustic Vintage Walnut accents. An over-scaled classic glass form pairs with T-style lamping to deliver a fresh take on modern-farmhouse style.



3266 IN
36" W, 15½" H
47¾" MAX. H**



3265 IN
18¼" DIA., 42¾" H (SHOWN)
42¾" MAX. H**



3267 IN
5¼" DIA., 16" H
46" MAX. H**



3263 IN
13¼" DIA., 36¾" H (SHOWN)
42¾" MAX. H**



3260 IN
5¼" W, 15¾" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3260 IN	1-60w Med.*		6¼"	3¾"	4¼" W, 7½" H Back Plate		
3263 IN	3-60w Med.*				10" Dia. Canopy	10'	3-6", 6-12"
3265 IN	5-60w Med.*				15" Dia. Canopy	10'	5-6", 10-12"
3266 IN	5-60w Med.*	5¼"			4¾" W, 12" L Canopy	10'	2-6", 4-12"
3267 IN	1-60w Med.*				5¼" Dia. Canopy	10'	1-6", 2-12"

*T-style bulbs included. **Maximum achievable height with stems included. Additional 12" stems available, 6033 IN.

WYATT™

FINISH IRON RUST
WITH WEATHERED ASH
SHADE OATMEAL
CHAMBRAY HARBACK

Reinventing a classic, Wyatt's bold design tames the Wild West. Its refined rustic silhouette reinterprets the wagon wheel in a solid wood polygonal ring tailored with modern sensibility. Deluxe details, such as textured metal brackets and candle sleeves, a wood-trimmed canopy and forged hooks enrich its luxe lodge appeal.



3918 IR
33¾" DIA., 21½" H



3916 IR
25" DIA., 16" H



3913 IR
19" DIA., 17" H



3910 IR
8½" W, 12½" H



3910 SH
5¼" W, 4½" H
(optional shade)



3916 IR
25" DIA., 16" H
(shown with optional shades)

ITEM	MAXIMUM WATTAGE	EXT.	TTO	BACK PLATE/CANOPY	WIRE	CHAIN
3910 IR	1-100w Med.	5½"	5¼"	4¾" W, 10¼" H Back Plate		
3913 IR	3-60w Cand.			6" Dia. Canopy	6'	5'
3916 IR	6-60w Cand.			8¼" Dia. Canopy	6'	3-5'
3918 IR	8-60w Cand.			8¼" Dia. Canopy	12'	4-5'
3910 SH	Do not exceed 40w					

CARTWRIGHT™

FINISH RUSTIC BRASS

The Cartwright pendant collection captures a modern farmhouse aesthetic with its minimalist silhouette enriched by exquisite details and rich finishes. Contrasting straps are enhanced by bold rivets while robust hooks add a masculine elegance.

ADDITIONAL FINISHES

Galvanized (GV), Polished Antique Nickel (PL)



3395 RS
19½" DIA., 25" H
59½" MAX. H*



3394 RS
15¼" DIA., 19¾" H
54¼" MAX. H*



3397 RS
11½" DIA., 14¾" H
49¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3394 RS	1-100w Med.	5" Dia.	10'	1-6", 2-12"
3395 RS	3-100w Med.	5" Dia.	10'	1-6", 2-12"
3397 RS	1-100w Med.	5" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 RS.

CARTWRIGHT™

FINISH GALVANIZED

The Cartwright pendant collection captures a modern farmhouse aesthetic with its minimalist silhouette enriched by exquisite details and rich finishes. Contrasting straps are enhanced by bold rivets while robust hooks add a masculine elegance.

ADDITIONAL FINISHES

Polished Antique Nickel (PL), Rustic Brass (RS)



3397 GV
11½" DIA., 14¾" H
49¼" MAX. H*



3395 GV
19½" DIA., 25" H
59½" MAX. H*



3394 GV
15¼" DIA., 19¾" H
54¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3394 GV	1-100w Med.	5" Dia.	10'	1-6", 2-12"
3395 GV	3-100w Med.	5" Dia.	10'	1-6", 2-12"
3397 GV	1-100w Med.	5" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 GV.

The Cartwright pendant collection captures a modern farmhouse aesthetic with its minimalist silhouette enriched by exquisite details and rich finishes. Contrasting straps are enhanced by bold rivets while robust hooks add a masculine elegance.

FINISH POLISHED ANTIQUE NICKEL

CARTWRIGHT™

ADDITIONAL FINISHES
Galvanized (GV), Rustic Brass (RS)



3394 PL
15¼" DIA., 19¾" H
54¼" MAX. H*



3395 PL
19½" DIA., 25" H
59½" MAX. H*



3397 PL
11½" DIA., 14¾" H
49¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3394 PL	1-100w Med.	5" Dia.	10'	1-6", 2-12"
3395 PL	3-100w Med.	5" Dia.	10'	1-6", 2-12"
3397 PL	1-100w Med.	5" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PL.

MIDDLETON™

FINISH
POLISHED NICKEL

This confident transitional design exemplifies that less is more. Possessing strong lines and seamless finishing, Middleton's solid metal construction is sleek and precise, available in either a commanding Polished Nickel finish or a rich Graphite Bronze finish with warm undertones.

ADDITIONAL FINISHES
Graphite Bronze (GZ)




3774 PN
26" DIA., 30" H
62¾" MAX. H*



3773 PN
20" DIA., 23½" H
56¼" MAX. H*



3777 PN
8" DIA., 12¾" H
45½" MAX. H*



3776 PN
52" W, 14" H
46¾" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
3773 PN	4-60w Cand.		5¼" Dia.	10'	1-6", 2-12"
3774 PN	4-60w Cand.		5¼" Dia.	10'	1-6", 2-12"
3776 PN	6-100w Med.	10"	4¾" W, 12" L	10'	2-6", 4-12"
3777 PN	1-100w Med.		5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3773 PN, 3776 PN and 3777 PN use 6031 PN. For 3774 PN use 6061 PN. Ideal for vintage filament bulbs (not included).

MIDDLETON™

FINISH
GRAPHITE BRONZE

This confident transitional design exemplifies that less is more. Possessing strong lines and seamless finishing, Middleton's solid metal construction is sleek and precise, available in either a commanding Polished Nickel finish or a rich Graphite Bronze finish with warm undertones.

ADDITIONAL FINISHES
Polished Nickel (PN)



3774 GZ
26" DIA., 30" H
62¾" MAX. H*



3773 GZ
20" DIA., 23½" H
56¼" MAX. H*



3777 GZ
8" DIA., 12¾" H
45½" MAX. H*



3776 GZ
52" W, 14" H
46¾" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
3773 GZ	4-60w Cand.		5¼" Dia.	10'	1-6", 2-12"
3774 GZ	4-60w Cand.		5¼" Dia.	10'	1-6", 2-12"
3776 GZ	6-100w Med.	10"	4¾" W, 12" L	10'	2-6", 4-12"
3777 GZ	1-100w Med.		5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3773 GZ, 3776 GZ and 3777 GZ use 6031 GZ. For 3774 GZ use 6061 GZ. Ideal for vintage filament bulbs (not included).

DAKOTA™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

The Dakota collection rounds up the best in Western style with a rustic chic design. Cast metal faux leather straps and buckle combine with clear seedy hurricane shades perched on cast cups for luxe lodge charm.

ADDITIONAL FINISHES
Polished Nickel (PL)



4789 OZ
29" DIA., 37" H



4786 OZ
26½" DIA., 36½" H



4784 OZ
18" DIA., 36" H



4780 OZ
5¾" W, 10½" H



4783 OZ
15¾" DIA., 27¼" H



4788 OZ
31½" DIA., 39¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4780 OZ	1-60w Cand.	5½"	6¼"	5¾" W, 8½" H Back Plate	
4783 OZ	3-60w Cand.			6½" Dia. Canopy	12', 10'
4784 OZ	6-60w Cand.			6½" Dia. Canopy	12', 10'
4786 OZ	6-60w Cand.			6½" Dia. Canopy	6', 5'
4788 OZ	8-60w Cand.			6½" Dia. Canopy	12', 10'
4789 OZ	9-60w Cand.			6½" Dia. Canopy	12', 10'

Ideal for vintage filament bulbs (not included).

DAKOTA™

FINISH POLISHED ANTIQUE NICKEL
GLASS CLEAR SEEDY

The Dakota collection rounds up the best in Western style with a rustic chic design. Cast metal faux leather straps and buckle combine with clear seedy hurricane shades perched on cast cups for luxe lodge charm.

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



4789 PL
29" DIA., 37" H



4786 PL
26½" DIA., 36½" H



4784 PL
18" DIA., 36" H



4780 PL
5¾" W, 10½" H



4783 PL
15¾" DIA., 27¼" H



4788 PL
31½" DIA., 39¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4780 PL	1-60w Cand.	5½"	6¼"	5¾" W, 8½" H Back Plate	
4783 PL	3-60w Cand.			6½" Dia. Canopy	12', 10'
4784 PL	6-60w Cand.			6½" Dia. Canopy	12', 10'
4786 PL	6-60w Cand.			6½" Dia. Canopy	6', 5'
4788 PL	8-60w Cand.			6½" Dia. Canopy	12', 10'
4789 PL	9-60w Cand.			6½" Dia. Canopy	12', 10'

Ideal for vintage filament bulbs (not included).

FENMORE™

FINISH
TEXTURED BRONZE

Fenmore is an updated traditional foyer lantern collection with bold hooks and a unique open work frame. The Textured Bronze finish adds depth and a classic modern flair.



4946 TZ
17" DIA., 35" H



4943 TZ
14½" DIA., 29" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
4943 TZ	3-60w Cand.	5¾" Dia.	12', 10'
4946 TZ	6-60w Cand.	5¾" Dia.	12', 10'

Pullman's mid-century modern pendant collection is inspired by a dramatic theater stage light design combined with a dash of nautical chic. A sleek white-painted interior reflector maximizes its downward illumination while simultaneously creating a striking contrast with the bold exterior.

FINISH BRUSHED NICKEL,
CHROME, OIL RUBBED BRONZE

PULLMAN™



ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3254 BN, CM, OZ	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3257 BN, CM, OZ	1-100w Med.	5½" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BN, CM, OZ.

CLANCY™

FINISH AGED ZINC
GLASS CLEAR

Clancy's transitional design features a clear glass urn, retro decorative construction elements and soft curves for an elegant style with vintage overtones.

Clancy Bath, page 373

ADDITIONAL FINISHES

Brushed Nickel (BN), Buckeye Bronze (KZ),
Polished Nickel (PN)



3030 DZ
6" W, 11¼" H



3034 DZ
19¼" DIA., 43½" H



3031 DZ
10" DIA., 15½" H
48¼" MAX. H*



3031 DZ
10" DIA., 16¼" H
(mounted as semi-flush)



3033 DZ
15½" DIA., 35¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
3030 DZ	1-100w Med.	6½"	5"	5" Dia. Back Plate		
3031 DZ	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
3033 DZ	3-60w Cand.			5" Dia. Canopy	12', 10'	
3034 DZ	4-60w Cand.			5" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 6037 DZ.

Clancy's transitional design features a clear glass urn, retro decorative construction elements and soft curves for an elegant style with vintage overtones.

Clancy Bath, page 373

FINISH POLISHED NICKEL
GLASS CLEAR

CLANCY™

ADDITIONAL FINISHES
Aged Zinc (DZ), Brushed Nickel (BN),
Buckeye Bronze (KZ)



3033 PN
15½" DIA., 35¼" H



3031 PN
10" DIA., 15½" H
48¼" MAX. H*



3034 PN
19¼" DIA., 43½" H



3030 PN
6" W, 11¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
3030 PN	1-100w Med.	6½"	5"	5" Dia. Back Plate		
3031 PN	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
3033 PN	3-60w Cand.			5" Dia. Canopy	12', 10'	
3034 PN	4-60w Cand.			5" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PN.

CLANCY™

FINISH BUCKEYE BRONZE
GLASS CLEAR

Clancy's transitional design features a clear glass urn, retro decorative construction elements and soft curves for an elegant style with vintage overtones.

Clancy Bath, page 373

ADDITIONAL FINISHES

Aged Zinc (DZ), Brushed Nickel (BN),
Polished Nickel (PN)



3030 KZ
6" W, 11¼" H



3034 KZ
19¼" DIA., 43½" H



3031 KZ
10" DIA., 15½" H
48¼" MAX. H*



3033 KZ
15½" DIA., 35¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
3030 KZ	1-100w Med.	6½"	5"	5" Dia. Back Plate		
3031 KZ	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
3033 KZ	3-60w Cand.			5" Dia. Canopy	12', 10'	
3034 KZ	4-60w Cand.			5" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 6037 KZ.

Clancy's transitional design features a clear glass urn, retro decorative construction elements and soft curves for an elegant style with vintage overtones.

Clancy Bath, page 373

FINISH BRUSHED NICKEL
GLASS CLEAR

CLANCY™

ADDITIONAL FINISHES
Aged Zinc (DZ), Buckeye Bronze (KZ),
Polished Nickel (PN)



3033 BN
15½" DIA., 35¼" H



3031 BN
10" DIA., 15½" H
48¼" MAX. H*



3034 BN
19¼" DIA., 43½" H



3030 BN
6" W, 11¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
3030 BN	1-100w Med.	6½"	5"	5" Dia. Back Plate		
3031 BN	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
3033 BN	3-60w Cand.			5" Dia. Canopy	12', 10'	
3034 BN	4-60w Cand.			5" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BN.

ELLIOTT™

FINISH ANTIQUE NICKEL,
GREYSTONE, REGENCY BRONZE

Elliott is a vintage replica of an authentic reflector pendant with classic details like cast turn knobs and a minimalist shade for timeless style.



3054 AN
13" DIA., 6¾" H
46" MAX. H*



3054 RB
13" DIA., 6¾" H
46" MAX. H*



3054 GS
13" DIA., 6¾" H
46" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3054 AN	1-100w Med.	4¾" Dia.	10'	1-6", 1-12", 1-18"
3054 GS	1-100w Med.	4¾" Dia.	10'	1-6", 1-12", 1-18"
3054 RB	1-100w Med.	4¾" Dia.	10'	1-6", 1-12", 1-18"

*Maximum achievable height with stems included. Additional 12" stems available, 6035 AN, HR. Ideal for vintage filament bulbs (not included).

A marriage of form and function, Barstow unites a vintage shape and industrial elements for a farmhouse chic statement. With its robust profile, bold finish options, prominent mesh screens and sturdy die-cast facets, Barstow is a perfect addition to a variety of interiors.

FINISH BUCKEYE BRONZE,
GALVANIZED

BARSTOW™



3604 GV
16¼" DIA., 12" H
45" MAX. H*



3604 KZ
16¼" DIA., 12" H
45" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3604 GV	1-100w Med.	5½" Dia.	10'	1-6", 2-12"
3604 KZ	1-100w Med.	5½" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 GV, KZ.

ELROY™

FINISH AGED ZINC, BRUSHED NICKEL, HERITAGE BRASS, OLDE BRONZE, POLISHED NICKEL
GLASS HOLOPHANE

Elroy's charming mini-pendant design features authentic details like cast knobs, clear ribbed optic glass and bold strap details in a variety of on-trend finish options. Edison style bulbs are the ideal companion, reinforcing Elroy's versatility and ability to enhance interiors ranging from traditional to industrial to modern farmhouse.



3097 OB
10" DIA., 10" H
43" MAX. H*




3097 BN
10" DIA., 10" H
43" MAX. H*



3097 HB
10" DIA., 10" H
43" MAX. H*



3097 DZ
10" DIA., 10" H
43" MAX. H*



3097 PN
10" DIA., 10" H
43" MAX. H*


ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3097 BN	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3097 DZ	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3097 HB	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3097 OB	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3097 PN	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4512 BN, OB and 6067 DZ, HB, PN.


Amelia's classic pendant design reinvents vintage details with a cast glass fitter, cast metal trim ring and ornamental clasps. The Polished White finish will infuse any space with a dash of fresh American style.

FINISH POLISHED WHITE
WITH POLISHED NICKEL

AMELIA™



3126 PT
13" DIA., 13" H
46" MAX. H*



3122 PT
11½" DIA., 9" H
42" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3122 PT	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3126 PT	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6067 PN.

AMELIA™

FINISH AGED ZINC, BUCKEYE BRONZE, POLISHED ANTIQUE NICKEL, POLISHED NICKEL

Amelia's classic pendant design reinvents vintage details with a cast shade fitter, cast metal trim ring and ornamental clasps. Bold finish options glow with retro inspiration.



3126 DZ
3126 DZ-LED
12¾" DIA., 14" H
47" MAX. H*



3126 PL
3126 PL-LED
12¾" DIA., 14" H
47" MAX. H*



3126 PN
3126 PN-LED
12¾" DIA., 14" H
47" MAX. H*



3126 KZ
3126 KZ-LED
12¾" DIA., 14" H
47" MAX. H*



INSTAFAVE



@designstorms
Joe Kwon Photography
THE AMELIA COLLECTION

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE	STEMS INCLUDED
3126 DZ	1-100w Med.	3126 DZ-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"
3126 KZ	1-100w Med.	3126 KZ-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"
3126 PL	1-100w Med.	3126 PL-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"
3126 PN	1-100w Med.	3126 PN-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4512 PL and 6067 PN, HB.


Amelia's classic pendant design reinvents vintage details with a cast shade fitter, cast metal trim ring and ornamental clasps. Bold finish options glow with retro inspiration.

FINISH AGED ZINC, BUCKEYE BRONZE, POLISHED ANTIQUE NICKEL, POLISHED NICKEL

AMELIA™



3122 KZ
11½" DIA., 9¾" H
42¾" MAX. H*



3122 PN
11½" DIA., 9¾" H
42¾" MAX. H*



3122 PL
11½" DIA., 9¾" H
42¾" MAX. H*



3122 DZ
11½" DIA., 9¾" H
42¾" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3122 DZ	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3122 KZ	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3122 PL	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3122 PN	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4512 PL and 6067 PN, HB.

AMELIA™

FINISH BUCKEYE BRONZE, CHROME,
POLISHED ANTIQUE NICKEL
GLASS ETCHED OPAL

Amelia's classic pendant design reinvents vintage details with a cast glass fitter, cast metal trim ring and ornamental clasps. Bold finish options glow with retro inspiration.



3124 CM
3124 CM-LED
12¾" DIA., 13¾" H
46¾" MAX. H*
T24



3124 KZ
3124 KZ-LED
12¾" DIA., 13¾" H
46¾" MAX. H*
T24



3124 PL
3124 PL-LED
12¾" DIA., 13¾" H
46¾" MAX. H*
T24



3127 KZ
3127 KZ-LED
11½" DIA., 9¾" H
42¾" MAX. H*
T24



3127 PL
3127 PL-LED
11½" DIA., 9¾" H
42¾" MAX. H*
T24



3127 CM
3127 CM-LED
11½" DIA., 9¾" H
42¾" MAX. H*
T24


ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE	STEMS INCLUDED
3124 CM	1-100w Med.	3124 CM-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"
3124 KZ	1-100w Med.	3124 KZ-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"
3124 PL	1-100w Med.	3124 PL-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"
3127 CM	1-100w Med.	3127 CM-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"
3127 KZ	1-100w Med.	3127 KZ-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"
3127 PL	1-100w Med.	3127 PL-LED	15w LED	900	2700K	90	1-75w	5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4512 CM, KZ, PL.

Amelia's classic pendant design reinvents vintage details with a cast glass fitter, cast metal trim ring and ornamental clasps. Bold finish options glow with retro inspiration.

FINISH BUCKEYE BRONZE, CHROME,
POLISHED ANTIQUE NICKEL
GLASS CLEAR SEEDY

AMELIA™



3123 KZ
11½" DIA., 9" H
42" MAX. H*



3123 PL
11½" DIA., 9" H
42" MAX. H*



3123 CM
11½" DIA., 9" H
42" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3123 CM	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3123 KZ	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"
3123 PL	1-100w Med.	5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4512 CM, KZ, PL. Ideal for vintage filament bulbs (not included).


FLETCHER™

FINISH AGED ZINC WITH
HERITAGE BRASS, AGED ZINC
WITH POLISHED NICKEL,
POLISHED NICKEL
GLASS ETCHED OPAL


Fletcher's chic vibe transcends style boundaries. A seamless dome shade features a cast-fitter and an elegant capture ring that secures the etched opal glass with decorative cast knobs. Spanning vintage to industrial, classic to transitional, Fletcher seamlessly unifies any décor declaration.




4836 DZ
22" DIA., 23" H
58" MAX. H*




4836 DZ-PN
22" DIA., 23" H
58" MAX. H*



4834 DZ
13½" DIA., 14½" H
49½" MAX. H*



4834 PN
13½" DIA., 14½" H
49½" MAX. H*



4834 DZ-PN
13½" DIA., 14½" H
49½" MAX. H*



4835 DZ
18" DIA., 19¾" H
54¾" MAX. H*



4835 DZ-PN
18" DIA., 19¾" H
54¾" MAX. H*


ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
4834 DZ	2-100w Med.	5½" Dia.	10'	1-6", 2-12"
4834 DZ-PN	2-100w Med.	5½" Dia.	10'	1-6", 2-12"
4834 PN	2-100w Med.	5½" Dia.	10'	1-6", 2-12"
4835 DZ	2-100w Med.	5½" Dia.	10'	1-6", 2-12"
4835 DZ-PN	2-100w Med.	5½" Dia.	10'	1-6", 2-12"
4836 DZ	3-100w Med.	5½" Dia.	10'	1-6", 2-12"
4836 DZ-PN	3-100w Med.	5½" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 4834 DZ, DZ-PN, PN use 6037 HB, PN. For 4835 DZ, DZ-PN and 4836 DZ, DZ-PN use 6067 HB, PN.

ACADEMY™

FINISH ENGLISH NICKEL WITH
POLISHED NICKEL, OIL RUBBED
BRONZE WITH HERITAGE BRASS
GLASS CLEAR SEEDY

The Academy collection combines a traditional Americana silhouette with modern sensibilities for a look that is effortlessly cool. At home in an urban loft or a modern farmhouse, Academy offers a range of hip, clear seedy glass shapes – choose the one that speaks to you.



67073 OZ
6½" DIA., 11" H
45" MAX. H*




67073 EN
6½" DIA., 11" H
45" MAX. H*




67071 OZ
5½" DIA., 13¼" H
47¼" MAX. H*



67071 EN
5½" DIA., 13¼" H
47¼" MAX. H*



67072 OZ
10" DIA., 10½" H
44½" MAX. H*



67072 EN
10" DIA., 10½" H
44½" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
67071 EN, OZ	1-100w Med.	5½" Dia.	10'	1-6", 2-12"
67072 EN, OZ	1-100w Med.	5½" Dia.	10'	1-6", 2-12"
67073 EN, OZ	1-100w Med.	5½" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 OZ and 6038 EN. Ideal for vintage filament bulbs (not included).

The Academy collection combines a traditional Americana silhouette with modern sensibilities for a look that is effortlessly cool. At home in an urban loft or a modern farmhouse, Academy offers a range of hip, clear seeded glass shapes – choose the one that speaks to you.

FINISH ENGLISH NICKEL WITH POLISHED NICKEL, OIL RUBBED BRONZE WITH HERITAGE BRASS
GLASS CLEAR SEEDY

ACADEMY™



67013 EN
6½" W, 12" H



67011 EN
5½" W, 14½" H



67012 EN
10" W, 11½" H



67013 OZ
6½" W, 12" H



67011 OZ
5½" W, 14½" H



67012 OZ
10" W, 11½" H

ITEM	MAXIMUM WATTAGE	CANOPY
67011 EN, OZ	1-100w Med.	5½" Dia.
67012 EN, OZ	1-100w Med.	5½" Dia.
67013 EN, OZ	1-100w Med.	5½" Dia.

Ideal for vintage filament bulbs (not included).

ACADEMY™

FINISH ENGLISH NICKEL WITH
POLISHED NICKEL, OIL RUBBED
BRONZE WITH HERITAGE BRASS
GLASS CLEAR SEEDY

The Academy collection combines a traditional Americana silhouette with modern sensibilities for a look that is effortlessly cool. At home in an urban loft or a modern farmhouse, Academy offers a range of hip, clear seedy glass shapes – choose the one that speaks to you.



67003 EN
6½" W, 13" H



67001 EN
5½" W, 15½" H



67002 EN
10" W, 12½" H



67003 OZ
6½" W, 13" H



67001 OZ
5½" W, 15½" H



67002 OZ
10" W, 12½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
67001 EN, OZ	1-100w Med.	8"	2¾"	5½" Dia.
67002 EN, OZ	1-100w Med.	10¾"	2¾"	5½" Dia.
67003 EN, OZ	1-100w Med.	9"	2¾"	5½" Dia.

Ideal for vintage filament bulbs (not included).

Congress is a traditional design that combines both hip and historical elements. This chic retro glass mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR SEEDY

CONGRESS™



31700 AN
6½" W, 13¼" H



31700 CM
6½" W, 13¼" H



31700 OZ
6½" W, 13¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
31700 AN	1-100w Med.	9"	4¾"	4¾"
31700 CM	1-100w Med.	9"	4¾"	4¾"
31700 OZ	1-100w Med.	9"	4¾"	4¾"

Ideal for vintage filament bulbs (not included).

CONGRESS™

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR, ETCHED OPAL

Congress is a traditional design that combines both hip and historical elements. This chic retro glass mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377



3170 AN (shown)
3170 CM
3170 OZ
8" W, 11¼" H



3173 AN
3173 CM (shown)
3173 OZ
7" W, 13½" H



3175 AN
3175 CM
3175 OZ (shown)
8¾" W, 13" H



3177 AN (shown)
3177 CM
3177 OZ
6" W, 14" H



3176 AN
3176 CM (shown)
3176 OZ
8" W, 11¼" H



3174 AN
3174 CM
3174 OZ (shown)
7" W, 13½" H



3171 AN (shown)
3171 CM
3171 OZ
8¾" W, 13" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3170 AN, CM, OZ	1-100w Med.	9¾"	4¾"	4¾" Dia.
3171 AN, CM, OZ	1-100w Med.	10"	4¾"	4¾" Dia.
3173 AN, CM, OZ	1-100w Med.	9¼"	4¾"	4¾" Dia.
3174 AN, CM, OZ	1-100w Med.	9¼"	4¾"	4¾" Dia.
3175 AN, CM, OZ	1-100w Med.	10"	4¾"	4¾" Dia.
3176 AN, CM, OZ	1-100w Med.	9¾"	4¾"	4¾" Dia.
3177 AN, CM, OZ	1-100w Med.	8¾"	4¾"	4¾" Dia.

Congress clear glass fixtures are ideal for vintage filament bulbs (not included).

Congress is a traditional design that combines both hip and historical elements. This chic retro glass mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-3797

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
SHADE SOLID AND WIRE METAL

CONGRESS™



3113 AN
9¼" W, 12" H



3113 CM
9¼" W, 12" H



3113 OZ
9¼" W, 12" H



3178 AN
9¾" W, 12¾" H



3178 CM
9¾" W, 12¾" H



3178 OZ
9¾" W, 12¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3113 AN, CM, OZ	1-100w Med.	10½"	4¾"	4¾" Dia.
3178 AN, CM, OZ	1-100w Med.	10½"	4¾"	4¾" Dia.

Congress wire shade fixtures are ideal for vintage filament bulbs (not included).

CONGRESS™

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
SHADE SOLID AND WIRE METAL

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377



3148 AN
9¾" DIA., 10½" H



3148 CM
9¾" DIA., 10½" H



3148 OZ
9¾" DIA., 10½" H



3114 AN
9¾" DIA., 10¼" H



3114 CM
9¾" DIA., 10¼" H



3114 OZ
9¾" DIA., 10¼" H

ITEM	MAXIMUM WATTAGE	CANOPY
3114 AN, CM, OZ	1-100w Med.	7" Dia.
3148 AN, CM, OZ	1-100w Med.	7" Dia.

Congress wire shade fixtures are ideal for vintage filament bulbs (not included).

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR, ETCHED OPAL

CONGRESS™



3140 AN
3140 CM
3140 OZ (shown)
8" DIA., 9½" H



3143 AN (shown)
3143 CM
3143 OZ
7" DIA., 11¼" H



3144 AN
3144 CM (shown)
3144 OZ
8¾" DIA., 11" H



3146 AN
3146 CM
3146 OZ (shown)
8" DIA., 9½" H



3147 AN (shown)
3147 CM
3147 OZ
12¼" DIA., 11¼" H



3149 AN
3149 CM (shown)
3149 OZ
7" DIA., 11¼" H



3150 AN
3150 CM
3150 OZ (shown)
8¾" DIA., 11" H



3151 AN (shown)
3151 CM
3151 OZ
7" DIA., 12" H

ITEM	MAXIMUM WATTAGE	CANOPY
3140 AN, CM, OZ	1-100w Med.	7" Dia.
3143 AN, CM, OZ	1-100w Med.	7" Dia.
3144 AN, CM, OZ	1-100w Med.	7" Dia.
3146 AN, CM, OZ	1-100w Med.	7" Dia.
3147 AN, CM, OZ	1-100w Med.	7" Dia.
3149 AN, CM, OZ	1-100w Med.	7" Dia.
3150 AN, CM, OZ	1-100w Med.	7" Dia.
3151 AN, CM, OZ	1-100w Med.	7" Dia.

Congress clear glass fixtures are ideal for vintage filament bulbs (not included).

CONGRESS ORDERING GUIDE




SCONCE, FLUSH & PENDANT

Outfit your space in retro-chic style!




Use the chart below to determine item numbers and specs for each Congress sconce, flush and pendant with clear, etched opal or clear seeded glass in three finish options.

<p>1 choose a style</p> <p>2 choose a finish</p> <p>3 choose a glass</p>	FINISH	CLEAR GLASS					ETCHED OPAL GLASS			CLEAR SEEDY
		Teardrop	Globe	Hurricane	Retro	Lg. Retro	Globe	Hurricane	Retro	Cylinder
										




SCONCE

	Antique Nickel	3177 AN 6" W 14" H	3174 AN 7" W 13½" H	3171 AN 8¾" W 13" H	3176 AN 8" W 11¼" H		3173 AN 7" W 13½" H	3175 AN 8¾" W 13" H	3170 AN 8" W 11¼" H	31700 AN 6½" W 13¼" H
	Chrome	3177 CM 6" W 14" H	3174 CM 7" W 13½" H	3171 CM 8¾" W 13" H	3176 CM 8" W 11¼" H		3173 CM 7" W 13½" H	3175 CM 8¾" W 13" H	3170 CM 8" W 11¼" H	31700 CM 6½" W 13¼" H
	Oil Rubbed Bronze	3177 OZ 6" W 14" H	3174 OZ 7" W 13½" H	3171 OZ 8¾" W 13" H	3176 OZ 8" W 11¼" H		3173 OZ 7" W 13½" H	3175 OZ 8¾" W 13" H	3170 OZ 8" W 11¼" H	31700 OZ 6½" W 13¼" H

FLUSH MOUNT

	Antique Nickel	3151 AN 6" W 12" H	3149 AN 7" W 11¼" H	3150 AN 8¾" W 11" H	3146 AN 8" W 9½" H	3147 AN 12¼" W 11¾" H	3143 AN 7" W 11¼" H	3144 AN 8¾" W 11" H	3140 AN 8" W 9½" H	
	Chrome	3151 CM 6" W 12" H	3149 CM 7" W 11¼" H	3150 CM 8¾" W 11" H	3146 CM 8" W 9½" H	3147 CM 12¼" W 11¾" H	3143 CM 7" W 11¼" H	3144 CM 8¾" W 11" H	3140 CM 8" W 9½" H	
	Oil Rubbed Bronze	3151 OZ 6" W 12" H	3149 OZ 7" W 11¼" H	3150 OZ 8¾" W 11" H	3146 OZ 8" W 9½" H	3147 OZ 12¼" W 11¾" H	3143 OZ 7" W 11¼" H	3144 OZ 8¾" W 11" H	3140 OZ 8" W 9½" H	

PENDANT


	Antique Nickel	3139 AN 6" W 10" H	3128 AN 7" W 9¼" H	3129 AN 8¾" W 9" H	3136 AN 8" W 7¼" H	3137 AN 12" W 9¾" H	3133 AN 7" W 9¼" H	3134 AN 8¾" W 9" H	3130 AN 8" W 7¼" H	
	Chrome	3139 CM 6" W 10" H	3128 CM 7" W 9¼" H	3129 CM 8¾" W 9" H	3136 CM 8" W 7¼" H	3137 CM 12" W 9¾" H	3133 CM 7" W 9¼" H	3134 CM 8¾" W 9" H	3130 CM 8" W 7¼" H	
	Oil Rubbed Bronze	3139 OZ 6" W 10" H	3128 OZ 7" W 9¼" H	3129 OZ 8¾" W 9" H	3136 OZ 8" W 7¼" H	3137 OZ 12" W 9¾" H	3133 OZ 7" W 9¼" H	3134 OZ 8¾" W 9" H	3130 OZ 8" W 7¼" H	

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS ETCHED OPAL

CONGRESS™



3130 AN
3130 CM (shown)
3130 OZ
8" DIA., 7¼" H
39¾" MAX. H*



3133 AN (shown)
3133 CM
3133 OZ
7" DIA., 9¼" H
41¾" MAX. H*



3134 AN
3134 CM
3134 OZ (shown)
8¾" DIA., 9" H
41½" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3130 AN, CM, OZ	1-100w Med.	4¾" Dia.	10'	1-6", 2-12"
3133 AN, CM, OZ	1-100w Med.	4¾" Dia.	10'	1-6", 2-12"
3134 AN, CM, OZ	1-100w Med.	4¾" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 AN and 4312 CM, OZ.

CONGRESS™

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR

Congress is a traditional design that combines both hip and historical elements. This chic retro glass mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377



3137 AN (shown)
3137 CM
3137 OZ
12¼" DIA., 9¾" H
42¼" MAX. H*



3136 AN
3136 CM
3136 OZ (shown)
8" DIA., 7¼" H
39¾" MAX. H*



3128 AN
3128 CM (shown)
3128 OZ
7" DIA., 9¼" H
41¾" MAX. H*



3129 AN (shown)
3129 CM
3129 OZ
8¾" DIA., 9" H
41½" MAX. H*



3139 AN
3139 CM
3139 OZ (shown)
6" DIA., 10" H
42½" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3128 AN, CM, OZ	1-100w Med.	4¾" Dia.	10'	1-6", 2-12"
3129 AN, CM, OZ	1-100w Med.	4¾" Dia.	10'	1-6", 2-12"
3136 AN, CM, OZ	1-100w Med.	4¾" Dia.	10'	1-6", 2-12"
3137 AN, CM, OZ	1-100w Med.	4¾" Dia.	10'	1-6", 2-12"
3139 AN, CM, OZ	1-100w Med.	4¾" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 AN and 4312 CM, OZ. Ideal for vintage filament bulbs (not included).

Congress is a traditional design that combines both hip and historical elements. This chic retro glass mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
SHADE SOLID AND WIRE METAL

CONGRESS™



3138 AN
9¾" DIA., 8½" H
41" MAX. H*

3138 CM
9¾" DIA., 8½" H
41" MAX. H*

3138 OZ
9¾" DIA., 8½" H
41" MAX. H*

3110 AN
9¼" DIA., 8¼" H
40¾" MAX. H*

3110 CM
9¼" DIA., 8¼" H
40¾" MAX. H*

3110 OZ
9¼" DIA., 8¼" H
40¾" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3110 AN, CM, OZ	1-100w Med.	4¾"	10'	1-6", 2-12"
3138 AN, CM, OZ	1-100w Med.	4¾"	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 AN and 4312 CM, OZ. Congress wire shade fixtures are ideal for vintage filament bulbs (not included).

CONGRESS™

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377



3198 AN
19¾" DIA., 43" H



3198 OZ
19¾" DIA., 43" H



3198 CM
19¾" DIA., 43" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3198 AN, CM, OZ	3-100w Med.	14½" Dia.	30'	3-6", 6-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 AN and 4312 CM, OZ. Ideal for vintage filament bulbs (not included).

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR

CONGRESS™



3046 AN (shown)
3046 CM
3046 OZ
26¼" DIA., 14" H
46¾" MAX. H*

3047 AN
3047 CM (shown)
3047 OZ
24¼" DIA., 17" H
49¾" MAX. H*

3041 AN
3041 CM
3041 OZ (shown)
27" DIA., 16" H
49" MAX. H*

3044 AN
3044 CM (shown)
3044 OZ
25¼" DIA., 16¼" H
49¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3041 AN, CM, OZ	4-100w Med.	4¾"	10'	1-4", 1-6", 2-12"
3044 AN, CM, OZ	4-100w Med.	4¾"	10'	1-4", 1-6", 2-12"
3046 AN, CM, OZ	4-100w Med.	4¾"	10'	1-4", 1-6", 2-12"
3047 AN, CM, OZ	4-100w Med.	4¾"	10'	1-4", 1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 AN and 4312 CM, OZ. Ideal for vintage filament bulbs (not included).

CONGRESS™

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS ETCHED OPAL

Congress is a traditional design that combines both hip and historical elements. This chic retro glass mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377



3045 AN
3045 CM (shown)
3045 OZ
27" DIA., 16" H
49" MAX. H*



3043 AN
3043 CM
3043 OZ (shown)
25¼" DIA., 16¼" H
49¼" MAX. H*



3040 AN (shown)
3040 CM
3040 OZ
26¼" DIA., 14" H
46¾" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3040 AN, CM, OZ	4-100w Med.	4¾"	10'	1-4", 1-6", 2-12"
3043 AN, CM, OZ	4-100w Med.	4¾"	10'	1-4", 1-6", 2-12"
3045 AN, CM, OZ	4-100w Med.	4¾"	10'	1-4", 1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 AN and 4312 CM, OZ.

Congress is a traditional design that combines both hip and historical elements. This chic retro glass mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

Congress Bath, pages 374-377

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
SHADE METAL

CONGRESS™



3048 AN
28" DIA., 15½" H
48¼" MAX. H*



3048 OZ
28" DIA., 15½" H
48¼" MAX. H*



3048 CM
28" DIA., 15½" H
48¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3048 AN, CM, OZ	4-100w Med.	4¾"	10'	1-4", 1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 AN and 4312 CM, OZ.

GATSBY™

FINISH HERITAGE BRASS
GLASS CLEAR

Gatsby has a retro modern aesthetic inspired by a vintage accordion-style elevator gate. Mid-century design details like authentic cast sockets and clear glass shades add to its nostalgic appeal.

ADDITIONAL FINISHES
Polished Antique Nickel (PL)



4935 HB
36" W, 34" H
57½" MAX. H*



4937 HB
4½" W, 8¼" H
41¾" MAX. H*



4933 HB
20¼" W, 34¼" H
59½" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
4933 HB	3-60w Med.	4½"	5¼" Dia.	10'	1-4", 1-6", 1-12"
4935 HB	5-60w Med.	4½"	4½" W, 7" L	10'	2-4", 2-6", 2-12"
4937 HB	1-60w Med.		5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6037 HB. Ideal for vintage filament bulbs (not included).

Gatsby has a retro modern aesthetic inspired by a vintage accordion-style elevator gate. Mid-century design details like authentic cast sockets and clear glass shades add to its nostalgic appeal.

FINISH POLISHED ANTIQUE NICKEL
GLASS CLEAR

GATSBY™


ADDITIONAL FINISHES
Heritage Brass (HB)



4933 PL
20¼" W, 34¼" H
59½" MAX. H*



4937 PL
4½" DIA., 8¼" H
41¾" MAX. H*



4935 PL
36" W, 34" H
57½" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
4933 PL	3-60w Med.	4½"	5¼" Dia.	10'	1-4", 1-6", 1-12"
4935 PL	5-60w Med.	4½"	4½" W, 7" L	10'	2-4", 2-6", 2-12"
4937 PL	1-60w Med.		5¼" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PL. Ideal for vintage filament bulbs (not included).



Rigby is inspired by the Americana barn light reborn as a chic interior retro classic. Features such as cast socket covers, mesh shades and canopy detail combine the best in both vintage and industrial design elements.

Rigby Bath, pages 378-379

FINISH POLISHED NICKEL

RIGBY™

ADDITIONAL FINISHES
Aged Zinc (DZ), Buckeye Bronze (KZ)



4360 PN
10" W, 8½" H



4367 PN
10" DIA., 4¼" H
37¼" MAX. H*



4364 PN
40" W, 7" H
39¼" MAX. H*



4363 PN
27" W, 16¾" H
51" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4360 PN	1-60w Med.		10½"	2½"	5" Dia. Back Plate		
4363 PN	3-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"
4364 PN	3-60w Med.	10"			4¾" W, 9" L Canopy	10'	2-6", 4-12"
4367 PN	1-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6067 PN. Ideal for vintage filament bulbs (not included).

RIGBY™

FINISH AGED ZINC

Rigby is inspired by the Americana barn light reborn as a chic interior retro classic. Features such as cast socket covers, mesh shades, canopy detail and two-tone finish options combine the best in both vintage and industrial design elements.

Rigby Bath, pages 378-379

ADDITIONAL FINISHES

Buckeye Bronze (KZ), Polished Nickel (PN)



4364 DZ
40" W, 7" H
39¼" MAX. H*

4367 DZ
10" DIA., 4¼" H
37¼" MAX. H*

4360 DZ
10" W, 8½" H

4363 DZ
27" W, 16¾" H
51" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4360 DZ	1-60w Med.		10½"	2½"	5" Dia. Back Plate		
4363 DZ	3-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"
4364 DZ	3-60w Med.	10"			4¾" W, 9" L Canopy	10'	2-6", 4-12"
4367 DZ	1-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6067 DZ. Ideal for vintage filament bulbs (not included).

Rigby is inspired by the Americana barn light reborn as a chic interior retro classic. Features such as cast socket covers, mesh shades, canopy detail and two-tone finish options combine the best in both vintage and industrial design elements.

Rigby Bath, pages 378-379

FINISH BUCKEYE BRONZE

RIGBY™

ADDITIONAL FINISHES
Aged Zinc (DZ), Polished Nickel (PN)



4360 KZ
10" W, 8½" H



4367 KZ
10" DIA., 4¼" H
37¼" MAX. H*



CEILING ADAPTER
83667 OZ
14½" DIA., 1¼" H
(shown with 4367 KZ)



4363 KZ
27" W, 16¾" H
51" MAX. H*



4364 KZ
40" W, 7" H
39¼" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4360 KZ	1-60w Med.		10½"	2½"	5" Dia. Back Plate		
4363 KZ	3-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"
4364 KZ	3-60w Med.	10"			4¾" W, 9" L Canopy	10'	2-6", 4-12"
4367 KZ	1-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6068 KZ. Ideal for vintage filament bulbs (not included).


REFINERY™

FINISH BLACK, BRUSHED
NICKEL, CHROME
GLASS CLEAR,
MIRRORED, SMOKED

Refinery is a chic interpretation of modern-industrial design. A variety of stylish glass and finish options ensure this pared down style can seamlessly add a dash of retro-modern charm to any space.



63306 BK-SM
43¾" W, 11¼" H
56" MAX. H*



63307 BN-CL
7¾" DIA., 12" H
56¾" MAX. H*



63307 BN-SM
7¾" DIA., 12" H
56¾" MAX. H*



63307 CM-MR
7¾" DIA., 12" H
56¾" MAX. H*



63307 CM-SM
7¾" DIA., 12" H
56¾" MAX. H*



63306 BK-CL
43¾" W, 11¼" H
56" MAX. H*



63307 BK-CL
7¾" DIA., 12" H
56¾" MAX. H*



63307 BK-SM
7¾" DIA., 12" H
56¾" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
63306 BK-CL	6-100w Med.	8¼"	4¾" W, 18½" L	10'	4-6", 6-12"
63306 BK-SM	6-100w Med.	8¼"	4¾" W, 18½" L	10'	4-6", 6-12"
63307 BK-CL	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 BK-SM	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 BN-CL	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 BN-SM	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 CM-MR	1-100w Med.		5" Dia.	10'	1-6", 3-12"
63307 CM-SM	1-100w Med.		5" Dia.	10'	1-6", 3-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6034 BK, BN, CM. Ideal for vintage filament bulbs (not included).

FINLEY™

FINISH BRUSHED NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Finley's modest composition makes a vintage statement with an austere, clean design. Three classic knurled knobs secure the clear seedy glass while a matching bottom trim ring completes the authentic look.



3687 BN
6" DIA., 8¾" H
53¼" MAX. H*

3687 CM
6" DIA., 8¾" H
53¼" MAX. H*

3687 OZ
6" DIA., 8¾" H
53¼" MAX. H*

3684 BN
10" DIA., 13½" H
58" MAX. H*

3684 CM
10" DIA., 13½" H
58" MAX. H*

3684 OZ
10" DIA., 13½" H
58" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3684 BN, CM, OZ	1-100w Med.	5" Dia.	10'	1-6", 3-12"
3687 BN, CM, OZ	1-100w Med.	5" Dia.	10'	1-6", 3-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BN, CM, OZ. Ideal for vintage filament bulbs (not included).

The Marlowe pendant collection offers traditional simplicity with bell-shaped seedy glass captured in a petite metal frame to create a graceful silhouette.

FINISH ANTIQUE NICKEL,
OIL RUBBED BRONZE
GLASS CLEAR SEEDY

MARLOWE™



3494 AN
11" DIA., 16¼" H



3497 AN
8¾" DIA., 12¾" H



3494 OZ
11" DIA., 16¼" H



3497 OZ
8¾" DIA., 12¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3494 AN, OZ	1-100w Med.	6" Dia.	12', 5'
3497 AN, OZ	1-100w Med.	6" Dia.	12', 10'

COLLIER™

FINISH ANTIQUE NICKEL
GLASS CLEAR SEEDY AND ETCHED

Collier's mid-century silhouette incorporates the best in retro simplicity. Cast knobs, hinges and stems in an Antique Nickel finish convey sleek elegance for a look that is at once modern and timeless.

ADDITIONAL FINISHES

Heritage Brass (HB), Light Oiled Bronze (LZ)



3385 AN
27" DIA., 30³/₄" H





3381 AN
3381 AN-LED
16½" DIA., 9¼" H



3382 AN
3382 AN-LED
22" DIA., 11½" H



3384 AN
21½" DIA., 24½" H



3380 AN
5¾" W, 16¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
3380 AN	1-100w Med.							5¾"	8"	5" Dia. Back Plate	
3381 AN	3-60w Cand.	3381 AN-LED	15w LED	1200	2700K	96	2-60w			6" Dia. Canopy	
3382 AN	4-60w Cand.	3382 AN-LED	20w LED	1800	2700K	96	3-60w			6" Dia. Canopy	
3384 AN	4-60w Cand.									5" Dia. Canopy	12', 10'
3385 AN	5-100w Med.									5" Dia. Canopy	6', 5'

For complete product details and LED specifications, refer to hinkleylighting.com. Ideal for vintage filament bulbs (not included).

COLLIER™

FINISH LIGHT OILED BRONZE
GLASS CLEAR SEEDY AND ETCHED

Collier's mid-century silhouette incorporates the best in retro simplicity. Cast knobs, hinges and stems in a Light Oiled Bronze finish convey sleek elegance for a look that is at once modern and timeless.

ADDITIONAL FINISHES

Antique Nickel (AN), Heritage Brass (HB)



3385 LZ
27" DIA., 30¾" H





3381 LZ
3381 LZ-LED
16½" DIA., 9¼" H



3382 LZ
3382 LZ-LED
22" DIA., 11½" H



3384 LZ
21½" DIA., 24½" H



3380 LZ
5¾" W, 16¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
3380 LZ	1-100w Med.							5¾"	8"	5" Dia. Back Plate	
3381 LZ	3-60w Cand.	3381 LZ-LED	15w LED	1200	2700K	96	2-60w			6" Dia. Canopy	
3382 LZ	4-60w Cand.	3382 LZ-LED	20w LED	1800	2700K	96	3-60w			6" Dia. Canopy	
3384 LZ	4-60w Cand.									5" Dia. Canopy	12', 10'
3385 LZ	5-100w Med.									5" Dia. Canopy	6', 5'

For complete product details and LED specifications, refer to hinkleylighting.com. Ideal for vintage filament bulbs (not included).

COLLIER™

FINISH HERITAGE BRASS
GLASS CLEAR SEEDY AND ETCHED

Collier's mid-century silhouette incorporates the best in retro simplicity. Cast knobs, hinges and stems in a Heritage Brass finish convey sleek elegance for a look that is at once modern and timeless.

ADDITIONAL FINISHES

Antique Nickel (AN), Light Oiled Bronze (LZ)



3385 HB
27" DIA., 30³/₄" H





3381 HB
3381 HB-LED
16½" DIA., 9¼" H



3382 HB
3382 HB-LED
22" DIA., 11½" H



3384 HB
21½" DIA., 24½" H



3380 HB
5¾" W, 16¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
3380 HB	1-100w Med.							5¾"	8"	5" Dia. Back Plate	
3381 HB	3-60w Cand.	3381 HB-LED	15w LED	1200	2700K	96	2-60w			6" Dia. Canopy	
3382 HB	4-60w Cand.	3382 HB-LED	20w LED	1800	2700K	96	3-60w			6" Dia. Canopy	
3384 HB	4-60w Cand.									5" Dia. Canopy	12', 10'
3385 HB	5-100w Med.									5" Dia. Canopy	6', 5'

For complete product details and LED specifications, refer to hinkleylighting.com. Ideal for vintage filament bulbs (not included).

HOWELL™

FINISH OIL RUBBED BRONZE
GLASS HOLOPHANE

Howell features a dramatic etched holophane glass orb suspended from bold Oil Rubbed Bronze decorative chain. With its vintage appeal, Howell achieves superior style from every angle.



3843 OZ
21½" DIA., 31½" H



3844 OZ
24¾" DIA., 38½" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3843 OZ	3-100w Med.	5¼" Dia.	10', 5'
3844 OZ	4-100w Med.	5¼" Dia.	10', 5'



BECKI OWENS
BECKIOWENS.COM
SOUTHERN CALIFORNIA

“Pendant lighting adds character to a space. I typically group pendants, especially in kitchen designs. Two or three fixtures give the space a wow factor.”

ABOVE: THE ODEON COLLECTION | 4744BN, PAGE 122

ODEON™

FINISH BRUSHED NICKEL,
OIL RUBBED BRONZE
GLASS INSIDE ETCHED HOLOPHANE

Inspired by the stylish Tribeca brasserie, Odeon elicits a fashionable, urban feel that is both modern and timeless. The metal frame follows the contour of the holophane sphere, inspiring perfection in any setting.



4744 BN
15" DIA., 18" H
54¼" MAX. H*



4744 OZ
15" DIA., 18" H
54¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
4744 BN	3-100w Med.	6" Dia.	10'	1-6", 2-12"
4744 OZ	3-100w Med.	6" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BN and 6037 OZ.

Chic and elegant, the Somerset collection exudes a quiet and precise sophistication. Subtly fusing modernity with vintage appeal, its etched opal glass deftly floats inside a streamlined metal yoke and ring while understated turned metal knobs add an authentic edge.

FINISH BRUSHED NICKEL,
BUCKEYE BRONZE, HERITAGE BRASS
GLASS ETCHED OPAL

SOMERSET™



3407 BN
11½" W, 17" H
49¾" MAX. H*



3407 HB
11½" W, 17" H
49¾" MAX. H*



3407 KZ
11½" W, 17" H
49¾" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3407 BN	1-100w Med.	6" Dia.	10'	1-6", 2-12"
3407 HB	1-100w Med.	6" Dia.	10'	1-6", 2-12"
3407 KZ	1-100w Med.	6" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4512 BN, HB and 6067 KZ.

ATRIUM™

FINISH BRONZE
GLASS ETCHED OPAL

Atrium's transitional chandelier design suggests an outer sphere constructed with two sets of parallel rings that intersect on each axis. The contemporary feel of the intersections is balanced by the rich Bronze finish to create a forged feel, softening its modern lines.



3275 BZ
26" DIA., 26¾" H
66¼" MAX. H*



3277 BZ
18¾" DIA., 19" H
58½" MAX. H*



3274 BZ
22" DIA., 22½" H
62" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3274 BZ	4-60w Cand.	5¼" Dia.	10'	1-6", 1-12", 1-18"
3275 BZ	4-100w Med.	5¼" Dia.	10'	1-6", 1-12", 1-18"
3277 BZ	1-100w Med.	5¼" Dia.	10'	1-6", 1-12", 1-18"

*Maximum achievable height with stems included. Additional 12" stems available, 6035 BZ.


Theory's multi-faceted cage design proves the ultimate style solution to the elegance equation. This vintage, mid-century design is updated with a sophisticated two-tone finish, enhancing its modern geometric shape with a bold layering effect.

FINISH AGED ZINC
WITH HERITAGE BRASS

THEORY™



3576 DZ
24¼" W, 17¾" H
52¼" MAX. H*



3574 DZ
15¼" W, 14¾" H
49" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3574 DZ	4-60w Cand.	5" Dia.	10'	1-6", 2-12"
3576 DZ	6-60w Cand.	5" Dia.	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3574 DZ use 6037 HB, and for 3576 DZ use 6067 HB. Ideal for vintage filament bulbs (not included).

ASTRID™

FINISH DELUXE GOLD
WITH METALLIC MATTE
BRONZE

Sleek and chic, Astrid is designed as an airy geometric beauty balanced with robust welded construction. The inner light cluster, uniquely wired from the bottom, appears to float inside the outer cage. The two-tone finish further enhances the layering effect for added depth and dimension.

ADDITIONAL FINISHES

Metallic Matte Bronze with Deluxe Gold (MM)



3025 DG
28" W, 34¼" H



3023 DG
20" W, 26¾" H



3027 DG
12" W, 10½" H
43¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN	STEMS INCLUDED
3023 DG	3-60w Cand.	5" Dia.	12', 10'	
3025 DG	5-60w Cand.	5" Dia.	12', 10'	
3027 DG	1-100w Med.	5" Dia.	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6030 DG. Ideal for vintage filament bulbs (not included).

Sleek and chic, Astrid is designed as an airy geometric beauty balanced with robust welded construction. The inner light cluster, uniquely wired from the bottom, appears to float inside the outer cage. The two-tone finish further enhances the layering effect for added depth and dimension.

FINISH METALLIC
MATTE BRONZE WITH
DELUXE GOLD

ASTRID™

ADDITIONAL FINISHES
Deluxe Gold with Metallic Matte Bronze (DG)



3027 MM
12" W, 10½" H
43¼" MAX. H*



3023 MM
20" W, 26¾" H



3025 MM
28" W, 34¼" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN	STEMS INCLUDED
3023 MM	3-60w Cand.	5" Dia.	12', 10'	
3025 MM	5-60w Cand.	5" Dia.	12', 10'	
3027 MM	1-100w Med.	5" Dia.	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6030 MM. Ideal for vintage filament bulbs (not included).

QUENTIN™

FINISH BUCKEYE BRONZE
WITH HERITAGE BRASS


Quentin is constructed of angular forms that create a striking geometric interplay. This stem-hung collection features intersecting rectangles in a bold Buckeye Bronze finish, forming a modern silhouette. Candle sleeves in Heritage Brass add a distinctively vintage feel that is both hip and historical.

ADDITIONAL FINISHES

Aged Zinc with Antique Nickel (DZ)



4815 KZ
36" W, 13" H
46" MAX. H**



4811 KZ
15" W, 9½" H
45¼" MAX. H**



4811 KZ
15" W, 13" H*
(can be mounted in a
close to ceiling position)



4813 KZ
8½" W, 14" H
47" MAX. H**



4814 KZ
17" W, 19¾" H
52¾" MAX. H**



4818 KZ
45" W, 13" H
46" MAX. H**

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
4811 KZ	4-60w Cand.	13"	4¾" Square	10'	1-6", 2-12"
4813 KZ	2-60w Cand.	7¾"	4¾" Square	10'	1-6", 2-12"
4814 KZ	4-60w Cand.	17"	4¾" Square	10'	1-6", 2-12"
4815 KZ	6-60w Cand.	16"	5" W, 11¾" L	10'	2-6", 4-12"
4818 KZ	8-60w Cand.	16"	5" W, 11¾" L	10'	2-6", 4-12"

*Minimum height when mounted close to ceiling. **Maximum achievable height with stems included. Additional 12" stems available, 6037 KZ. Ideal for vintage filament bulbs (not included).

QUENTIN™

FINISH AGED ZINC
WITH ANTIQUE NICKEL

Quentin is constructed of angular forms that create a striking geometric interplay. This stem-hung collection features intersecting rectangles in a bold Aged Zinc finish, forming a modern silhouette. Candle sleeves in Antique Nickel add a distinctively vintage feel that is both hip and historical.

ADDITIONAL FINISHES

Buckeye Bronze with Heritage Brass (KZ)



4815 DZ
36" W, 13" H
46" MAX. H**



4811 DZ
15" W, 9½" H
45¼" MAX. H**



4811 DZ
15" W, 13" H*
(can be mounted in a
close to ceiling position)



4813 DZ
8½" W, 14" H
47" MAX. H**



4814 DZ
17" W, 19¾" H
52¾" MAX. H**



4818 DZ
45" W, 13" H
46" MAX. H**

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE	STEMS INCLUDED
4811 DZ	4-60w Cand.	13"	4¾" Square	10'	1-6", 2-12"
4813 DZ	2-60w Cand.	7¾"	4¾" Square	10'	1-6", 2-12"
4814 DZ	4-60w Cand.	17"	4¾" Square	10'	1-6", 2-12"
4815 DZ	6-60w Cand.	16"	5" W, 11¾" L	10'	2-6", 4-12"
4818 DZ	8-60w Cand.	16"	5" W, 11¾" L	10'	2-6", 4-12"

*Minimum height when mounted close to ceiling. **Maximum achievable height with stems included. Additional 12" stems available, 6037 DZ. Ideal for vintage filament bulbs (not included).

FULTON™

FINISH AGED ZINC
WITH ANTIQUE NICKEL
SHADE BLACK LINEN

Fulton's minimalist beauty emphasizes 'less is more' with vintage industrial style. This clean, airy tapered cage design is constructed without glass and the unique square candle sleeves rest on a discreet "H"-shaped cluster.

ADDITIONAL FINISHES

Bronze with Heirloom Brass (BZ)



3358 DZ
33½" W, 54¾" H
93¾" MAX. H*





3357 DZ
27³/₄" W, 46¹/₄" H
85¹/₄" MAX. H*



3351 DZ
10" W, 12¹/₄" H
51" MAX. H*




3336 DZ
22" W, 24¹/₂" H
69" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3336 DZ	4-60w Cand.	5" Dia.	10'	1-6", 3-12"
3351 DZ	1-100w Med.	5" Dia.	10'	1-6", 1-12", 1-18"
3357 DZ	7-100w Med.	5" Dia.	10'	1-6", 1-12", 1-18"
3358 DZ	13-75w Med.	5" Dia.	10'	1-6", 1-12", 1-18", 1-30"

*Maximum achievable height with stems included. Additional 12" stems available. For 3336 DZ and 3351 DZ use 6035 AN. For 3357 DZ and 3358 DZ use 6065 AN. Ideal for vintage filament bulbs (not included).



3334 DZ
18" W, 16¼" H
61" MAX. H*




3337 DZ
10" W, 8¾" H
47½" MAX. H*



3330 DZ
7½" W, 22¼" H



3330 DZ
(side view)



3338 DZ
48" W, 16¼" H
60¼" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3330 DZ	2-60w Cand.		5"	11¼"	7½" W, 22¼" H Back Plate		
3334 DZ	4-60w Cand.				5" Dia. Canopy	10'	1-6", 3-12"
3337 DZ	1-100w Med.				5" Dia. Canopy	10'	1-6", 1-12", 1-18"
3338 DZ	8-60w Cand.	18"			4¾" W, 9½" L Canopy	10'	2-6", 6-12"


*Maximum achievable height with stems included. Additional 12" stems available, 6035 AN. Ideal for vintage filament bulbs (not included).




3332 DZ
13½" W, 9¼" H



3332 DZ
10" W, 7½" H
(shown without shades)




3335 DZ
50" W, 9" H
53" MAX. H*



3355 DZ
65" W, 9¾" H
53¾" MAX. H*

@INSTAFAVE



@magdalenaland.ca
THE FULTON COLLECTION

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3332 DZ	2-60w Cand.		4½***, 6¼"	3¾***, 5¾"	5" W, 7½" H Back Plate		
3335 DZ	5-100w Med.	10"			4¾" W, 9½" L Canopy	10'	2-6", 6-12"
3355 DZ	7-100w Med.	10"			4¾" W, 14½" L Canopy	10'	2-6", 6-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3335 DZ use 6035 AN, and for 3355 DZ use 6065 AN. Ideal for vintage filament bulbs (not included). **Without shades.

FULTON™

FINISH BRONZE WITH
HEIRLOOM BRASS
SHADE MOCHA LINEN
WITH ESPRESSO TRIM

Fulton's minimalist beauty emphasizes 'less is more' with vintage industrial style. This clean, airy tapered cage design is constructed without glass and the unique square candle sleeves rest on a discreet "H"-shaped cluster.

ADDITIONAL FINISHES

Aged Zinc with Antique Nickel (DZ)

@INSTAFAVE



@studiothomas

THE FULTON COLLECTION



3358 BZ
33½" W, 54¾" H
93¾" MAX. H*





3357 BZ
27¾" W, 46¼" H
85¼" MAX. H*



3351 BZ
10" W, 12¼" H
51" MAX. H*



3336 BZ
22" W, 24½" H
69" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3336 BZ	4-60w Cand.	5" Dia.	10'	1-6", 3-12"
3351 BZ	1-100w Med.	5" Dia.	10'	1-6", 1-12", 1-18"
3357 BZ	7-100w Med.	5" Dia.	10'	1-6", 1-12", 1-18"
3358 BZ	13-75w Med.	5" Dia.	10'	1-6", 1-12", 1-18", 1-30"

*Maximum achievable height with stems included. Additional 12" stems available. For 3336 BZ and 3351 BZ use 6035 HR. For 3357 BZ and 3358 BZ use 6065 HR. Ideal for vintage filament bulbs (not included).



3334 BZ
18" W, 16¼" H
61" MAX. H*



3337 BZ
10" W, 8¾" H
47½" MAX. H*



3330 BZ
7½" W, 22¼" H



3330 BZ
(side view)



3338 BZ
48" W, 16¼" H
60¼" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3330 BZ	2-60w Cand.		5"	11¼"	7½" W, 22¼" H Back Plate		
3334 BZ	4-60w Cand.				5" Dia. Canopy	10'	1-6", 3-12"
3337 BZ	1-100w Med.				5" Dia. Canopy	10'	1-6", 1-12", 1-18"
3338 BZ	8-60w Cand.	18"			4¾" W, 9½" L Canopy	10'	2-6", 6-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6035 HR. Ideal for vintage filament bulbs (not included).




3335 BZ
50" W, 9" H
53" MAX. H*



3332 BZ
13½" W, 9¼" H



3332 BZ
10" W, 7½" H
(shown without shades)



3355 BZ
65" W, 9¼" H
53¾" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3332 BZ	2-60w Cand.		4½***, 6¼"	3¾***, 5¾"	5" W, 7½" H Back Plate		
3335 BZ	5-100w Med.	10"			4¾" W, 9½" L Canopy	10'	2-6", 6-12"
3355 BZ	7-100w Med.	10"			4¾" W, 14½" L Canopy	10'	2-6", 6-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3335 BZ use 6035 HR, and for 3355 BZ use 6065 HR. Ideal for vintage filament bulbs (not included). **Without shades.

BOYER™

FINISH AGED ZINC
WITH ANTIQUE NICKEL

Industrial and polished, Boyer's charming mid-century modern style will add an element of history to any space. Two-tone finishes and contrasting reflectors are an ideal match with vintage filament bulbs for timeless style with a twist.

Boyer Bath, pages 368-369

ADDITIONAL FINISHES

Oil Rubbed Bronze with Brushed Bronze (OZ)



4538 DZ
34¾" DIA., 27" H
60¾" MAX. H*



4530 DZ
7" W, 9" H



4534 DZ
24" DIA., 19¼" H
52¾" MAX. H*



4535 DZ
28" DIA., 22½" H
56" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4530 DZ	1-100w Med.	5.5"	3.5"	6" Dia. Back Plate		
4534 DZ	4-100w Med.			6½" Dia. Canopy	10'	1-6", 2-12"
4535 DZ	5-100w Med.			6½" Dia. Canopy	10'	1-6", 2-12"
4538 DZ	9-100w Med.			6½" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 4534 DZ and 4535 DZ, use 4312 AN. For 4538 DZ, use 4512 AN6. Ideal for vintage filament bulbs (not included).

BOYER™

FINISH OIL RUBBED BRONZE
WITH BRUSHED BRONZE

Industrial and polished, Boyer's charming mid-century modern style will add an element of history to any space. Two-tone finishes and contrasting reflectors are an ideal match with vintage filament bulbs for timeless style with a twist.

Boyer Bath, pages 368-369

ADDITIONAL FINISHES

Aged Zinc with Antique Nickel (DZ)



4538 OZ
34¾" DIA., 27" H
60¾" MAX. H*



4534 OZ
24" DIA., 19¼" H
52¾" MAX. H*



5260 OZ
7" W, 9" H



4535 OZ
28" DIA., 22½" H
56" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4534 OZ	4-100w Med.			6½" Dia. Canopy	10'	1-6", 2-12"
4535 OZ	5-100w Med.			6½" Dia. Canopy	10'	1-6", 2-12"
4538 OZ	9-100w Med.			6½" Dia. Canopy	10'	1-6", 2-12"
5260 OZ	1-100w Med.	5.5"	3.5"	6" Dia. Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available. For 4534 OZ and 4535 OZ, use 6036 OZ. For 4538 OZ, use 6066 OZ. Ideal for vintage filament bulbs (not included).

FULHAM™

FINISH BUCKEYE BRONZE
WITH HERITAGE BRASS
GLASS CLEAR BEVELED

Fulham's bold orb design showcases clear beveled glass lenses that punctuate the minimalist elegance with an industrial edge. Its sleek lines combine with cast sockets and mid-century elements for a dynamic transitional style.

ADDITIONAL FINISHES
Polished Antique Nickel (PL)



3927 KZ
7¾" W, 9" H
42" MAX. H*



3925 KZ
32" DIA., 32½" H
69¼" MAX. H*



3924 KZ
26" DIA., 26½" H
63¼" MAX. H*



3920 KZ
7¾" W, 21½" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3920 KZ	1-100w Med.		5"	10¾"	7½" Dia. Back Plate		
3924 KZ	4-100w Med.				5" Dia. Canopy	10'	1-6", 2-12"
3925 KZ	5-100w Med.				5" Dia. Canopy	10'	1-6", 2-12"
3927 KZ	1-100w Med.	4½"			5" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3924 KZ and 3927 KZ, use 6037 HB. For 3925 KZ, use 6067 HB. Ideal for vintage filament bulbs (not included).

Fulham's bold orb design showcases clear beveled glass lenses that punctuate the minimalist elegance with an industrial edge. Its sleek lines combine with cast sockets and mid-century elements for a dynamic transitional style.

FINISH POLISHED
ANTIQUE NICKEL
GLASS CLEAR BEVELED

FULHAM™

ADDITIONAL FINISHES
Buckeye Bronze with Heritage Brass (KZ)



3924 PL
26" DIA., 26½" H
6¾" MAX. H*



3920 PL
7¾" W, 21½" H



3925 PL
32" DIA., 32½" H
69¼" MAX. H*



3927 PL
7¾" W, 9" H
42" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3920 PL	1-100w Med.		5"	10¾"	7½" Dia. Back Plate		
3924 PL	4-100w Med.				5" Dia. Canopy	10'	1-6", 2-12"
3925 PL	5-100w Med.				5" Dia. Canopy	10'	1-6", 2-12"
3927 PL	1-100w Med.	4½"			5" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3924 PL and 3927 PL, use 4312 PL. For 3925 PL, use 4512 PL. Ideal for vintage filament bulbs (not included).

TERRA™

FINISH OILED BRONZE
WITH HERITAGE BRASS

Terra combines mid-century modern and contemporary design elements for a dramatic silhouette. Intersecting vertical and horizontal lines form a stylish, open globe suspended from a sleek stem.

ADDITIONAL FINISHES

Polished Nickel (PN)



3514 OR
13" DIA., 13¾" H
48½" MAX. H*



3515 OR
19" DIA., 20" H
54¾" MAX. H*



3512 OR
10" W, 10" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3512 OR	2-60w Cand.	5¼"	5"	4½" W, 8" H Back Plate		
3514 OR	3-60w Cand.			4¾" Dia. Canopy	10'	1-6", 2-12"
3515 OR	5-60w Cand.			4¾" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 OR. Ideal for vintage filament bulbs (not included).

Terra combines mid-century modern and contemporary design elements for a dramatic silhouette. Intersecting vertical and horizontal lines form a stylish, open globe suspended from a sleek stem.

FINISH POLISHED NICKEL

TERRA™

ADDITIONAL FINISHES
Oiled Bronze with Heritage Brass (OR)



3512 PN
10" W, 10" H



3515 PN
19" DIA., 20" H
54¼" MAX. H*



3514 PN
13" DIA., 13¾" H
48½" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3512 PN	2-60w Cand.	5¼"	5"	4½" W, 8" H Back Plate		
3514 PN	3-60w Cand.			4¾" Dia. Canopy	10'	1-6", 2-12"
3515 PN	5-60w Cand.			4¾" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PN. Ideal for vintage filament bulbs (not included).

EUCLID™

FINISH CEMENT GRAY
WITH BRUSHED GOLD

Euclid is a unique style that defies trends. Blending traditional warmth and contemporary flair, its bold proportions and rich two-tone finish create a stunning silhouette.

ADDITIONAL FINISHES

Spanish Bronze with Heirloom Brass (SB)



3464 CG
44" DIA., 49" H

50



3468 CG
28¼" DIA., 33" H



3469 CG
36" DIA., 41" H



3460 CG
9½" W, 20" H



3463 CG
20" DIA., 24½" H



3466 CG
21¼" DIA., 25¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
3460 CG	2-60w Cand.	5½"	10"	4½" W, 9" H Back Plate	
3463 CG	3-60w Cand.			7" Dia. Canopy	12', 10'
3464 CG	16-60w Cand.			7" Dia. Canopy	12', 10'
3466 CG	6-60w Cand.			7" Dia. Canopy	12', 10'
3468 CG	8-60w Cand.			7" Dia. Canopy	12', 10'
3469 CG	12-60w Cand.			7" Dia. Canopy	12', 10'

Ideal for vintage filament bulbs (not included).

EUCLID™

FINISH SPANISH BRONZE
WITH HEIRLOOM BRASS

Euclid is a unique style that defies trends. Blending traditional warmth and contemporary flair, its bold proportions and rich two-tone finish create a stunning silhouette.

ADDITIONAL FINISHES

Cement Gray with Brushed Gold (CG)



3464 SB
44" DIA., 49" H





3468 SB
28¼" DIA., 33" H



3469 SB
36" DIA., 41" H



3460 SB
9½" W, 20" H



3463 SB
20" DIA., 24½" H



3466 SB
21¼" DIA., 25¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
3460 SB	2-60w Cand.	5½"	10"	4½" W, 9" H Back Plate	
3463 SB	3-60w Cand.			7" Dia. Canopy	12', 10'
3464 SB	16-60w Cand.			7" Dia. Canopy	12', 10'
3466 SB	6-60w Cand.			7" Dia. Canopy	12', 10'
3468 SB	8-60w Cand.			7" Dia. Canopy	12', 10'
3469 SB	12-60w Cand.			7" Dia. Canopy	12', 10'

Ideal for vintage filament bulbs (not included).

MARGEUX™

FINISH VINTAGE BRASS
GLASS ETCHED OPAL

Margeaux's traditional style is reinforced by an impressive formal presence. This combination stem and chain hung collection features cast transition elements that extend from the circular body to the torchère arms, while the Vintage Brass finish complements this open airy design.

ADDITIONAL FINISHES
Polished Nickel (PN)

INSTAFAVE



@andreaporrirt

THE MARGEUX COLLECTION



3588 VS
36" DIA., 32" H



3580 VS
4½" W, 18" H



3582 VS
12¾" W, 18" H



3587 VS
3½" DIA., 14¼" H
47¼" MAX. H*



3585 VS
26" DIA., 21¼" H
64" MAX. H*



3586 VS
29" DIA., 24½" H
67¼" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
3580 VS	1-100w Med.	5¾"	9½"	4½" W, 8" H Back Plate		
3582 VS	2-100w Med.	5¾"	9½"	4½" W, 8" H Back Plate		
3585 VS	5-100w Med.			5" Dia. Canopy	12' Wire	1-4", 1-6", 1-12", 1-18"
3586 VS	6-100w Med.			5" Dia. Canopy	12' Wire	1-4", 1-6", 1-12", 1-18"
3587 VS	1-100w Med.			5" Dia. Canopy	12' Wire	1-6", 2-12"
3588 VS	8-100w Med.			6" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 6212 VS.

MARGEAUX™

FINISH POLISHED NICKEL
GLASS ETCHED OPAL

Margeaux's traditional style is reinforced by an impressive formal presence. This combination stem and chain hung collection features cast transition elements that extend from the circular body to the torchère arms, while the Polished Nickel finish complements this open airy design.

ADDITIONAL FINISHES
Vintage Brass (VS)



3588 PN
36" DIA., 32" H



3580 PN
4½" W, 18" H



3582 PN
12¾" W, 18" H



3587 PN
3½" DIA., 14¼" H
47¼" MAX. H*



3585 PN
26" DIA., 21¼" H
64" MAX. H*



3586 PN
29" DIA., 24½" H
67¼" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
3580 PN	1-100w Med.	5¾"	9½"	4½" W, 8" H Back Plate		
3582 PN	2-100w Med.	5¾"	9½"	4½" W, 8" H Back Plate		
3585 PN	5-100w Med.			5" Dia. Canopy	12' Wire	1-4", 1-6", 1-12", 1-18"
3586 PN	6-100w Med.			5" Dia. Canopy	12' Wire	1-4", 1-6", 1-12", 1-18"
3587 PN	1-100w Med.			5" Dia. Canopy	12' Wire	1-6", 2-12"
3588 PN	8-100w Med.			6" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 6212 PN.

ZELDA™

FINISH POLISHED NICKEL
 GLASS ETCHED
 SHADE TEXTURED OFF-WHITE LINEN

Zelda's striking mid-century silhouette features spheres that increase in size as they descend from the top loop, creating an elegant seamless center column. The sleek rectangular bowed arms support tapered etched glass shades perched on a hemisphere cup, adding vintage appeal.

ADDITIONAL FINISHES

Vintage Brass (VS)



3441 PN
 14¾" DIA., 12½" H



3440 PN
 5½" W, 11¾" H



3444 PN
 20¼" DIA., 18½" H



3447 PN
 4¾" DIA., 12½" H
 44¾" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
3440 PN	1-100w Med.	5¾"	6¾"	5½" Dia. Back Plate		
3441 PN	3-100w Med.			5½" Dia. Canopy		
3444 PN	3-100w Med.			5½" Dia. Canopy	12', 10'	
3447 PN	1-100w Med.			5½" Dia. Canopy	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PN.

Zelda's striking mid-century silhouette features spheres that increase in size as they descend from the top loop, creating an elegant seamless center column. The sleek rectangular bowed arms support tapered etched glass shades perched on a hemisphere cup, adding vintage appeal.

FINISH VINTAGE BRASS
GLASS ETCHED
SHADE TEXTURED OFF-WHITE LINEN

ZELDA™

ADDITIONAL FINISHES
Polished Nickel (PN)



3447 VS
4¾" DIA., 12½" H
44¾" MAX. H*



3444 VS
20¼" DIA., 18½" H



3441 VS
14¾" DIA., 12½" H



3440 VS
5½" W, 11¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
3440 VS	1-100w Med.	5¾"	6¾"	5½" Dia. Back Plate		
3441 VS	3-100w Med.			5½" Dia. Canopy		
3444 VS	3-100w Med.			5½" Dia. Canopy	12', 10'	
3447 VS	1-100w Med.			5½" Dia. Canopy	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 VS.

ASCHER™

FINISH BRUSHED CARAMEL
 SHADE BLACK GOLD-LINED
 (OPTIONAL) OR BLACK ORGANZA
 (OPTIONAL), BLACK ORGANZA
 (4753 BC, INCLUDED)

Ascher dazzles with a brilliant faceted solid crystal center column and stunning crystal bobeches. The streamlined arms in a luxe Brushed Caramel finish and optional black gold-lined or black organza shades reinforce its sleek, chic transitional design.

ADDITIONAL FINISHES

Polished Nickel (PN)



4756 BC
 28" DIA., 28¼" H



4750 SH
 5" DIA., 4½" H
 (optional shade)



4752 SH
 5" DIA., 4½" H
 (optional shade)



4750 BC
 4¾" W, 17¾" H



4752 BC
 12" W, 17¾" H



4753 BC
 21¼" W, 23¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4750 BC	1-60w Cand.	6¼"	12¾"	4¾" W, 6" H Back Plate	
4750 SH	Do not exceed 40w				
4752 BC	2-60w Cand.	5"	12¾"	4¾" W, 6" H Back Plate	
4752 SH	Do not exceed 40w				
4753 BC	3-60w Cand.			6" Dia. Canopy	12', 10'
4756 BC	6-60w Cand.			6" Dia. Canopy	12', 10'

Ascher dazzles with a brilliant faceted solid crystal center column and stunning crystal bobeches. The streamlined arms in a luxe Polished Nickel finish and optional black gold-lined or black organza shades reinforce its sleek, chic transitional design.

FINISH POLISHED NICKEL
 SHADE BLACK GOLD-LINED
 (OPTIONAL) OR BLACK ORGANZA
 (OPTIONAL), BLACK ORGANZA
 (4753 PN, INCLUDED)

ASCHER™

ADDITIONAL FINISHES
 Brushed Caramel (BC)



4752 PN
 12" W, 17¾" H



4750 PN
 4¾" W, 17¾" H



4753 PN
 21¼" W, 23¼" H



4756 PN
 28" DIA., 28¼" H



4752 SH
 5" DIA., 4½" H
 (optional shade)



4750 SH
 5" DIA., 4½" H
 (optional shade)

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4750 PN	1-60w Cand.	6¼"	12¾"	4¾" W, 6" H Back Plate	
4750 SH	Do not exceed 40w				
4752 PN	2-60w Cand.	5"	12¾"	4¾" W, 6" H Back Plate	
4752 SH	Do not exceed 40w				
4753 PN	3-60w Cand.			6" Dia. Canopy	12', 10'
4756 PN	6-60w Cand.			6" Dia. Canopy	12', 10'

LARA™

FINISH BRUSHED SILVER
GLASS ANTIQUE MIRROR

Stunning octagonal panes of antique mirror glass are the striking centerpiece of Lara's stem hung transitional design. The hand painted Brushed Silver finish radiates with lustrous undertones, adding dimension and vintage elegance.



3566 BV
26¼" DIA., 13¾" H
46½" MAX. H*



3560 BV
8½" W, 11½" H



3563 BV
15" DIA., 8¼" H



3567 BV
8½" DIA., 12¼" H
44¾" MAX. H*



3564 BV
21¼" DIA., 12¾" H
45½" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3560 BV	1-60w Cand.	4"	5¾"	8½" W, 11½" H Back Plate		
3563 BV	3-100w Med.			10¼" Dia. Canopy		
3564 BV	5-60w Cand.			5¼" Dia. Canopy	10'	1-6", 2-12"
3566 BV	8-60w Cand.			5¼" Dia. Canopy	10'	1-6", 2-12"
3567 BV	1-100w Med.			5¼" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available. For 3564 BV and 3565 BV, use 6063 BV. For 3567 BV, use 6033 BV.

LARCHMERE™

FINISH ENGLISH NICKEL
SHADE WHITE LINEN
HARDBACK

Combining the clean lines of an angular, architectural frame with a white linen hardback drum shade, Larchmere elevates the minimalist geometric form to a new level of transitional elegance. Subtly integrating chic design elements, from a heavy crystal center column, metal trim shade detailing an etched glass lens, underscore an attention to detail that yields Larchmere's discerning silhouette.



4485 EN
28" DIA., 21" H
59½" MAX. H*



4483 EN
18" DIA., 13¾" H



4484 EN
24" DIA., 20¾" H
59¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
4483 EN	3-100w Med.	6¾" Dia.		
4484 EN	4-100w Med.	6¾" Dia.	10'	2-6", 2-12"
4485 EN	4-100w Med.	6¾" Dia.	10'	2-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6038 EN.

BLAKELY™

FINISH BRUSHED NICKEL
SHADE DUNE HEATHERED LINEN

The Blakely collection defines soft modern elegance with a sleek intersecting outer frame that seamlessly encloses a sophisticated heathered fabric drum shade.

ADDITIONAL FINISHES

Buckeye Bronze (KZ)



3796 BN
22" DIA., 35½" H



3797 BN
12" DIA., 16" H
60½" MAX. H**



3794 BN
24" DIA., 12½" H
55¼" MAX. H**
includes bottom acrylic lens



3794 BN
24" DIA., 15¼" H*
includes bottom acrylic lens
(mounted as semi-flush)



3793 BN
16½" DIA., 27" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN	STEMS INCLUDED
3793 BN	3-60w Cand.	5½" Dia.	12', 10'	
3794 BN	4-100w Med.	5½" Dia.	10' Wire	1-4", 1-6", 1-12", 1-18"
3796 BN	4-100w Med.	5½" Dia.	12', 10'	
3797 BN	1-100w Med.	5½" Dia.	12' Wire	1-6", 3-12"

*Minimum height when mounting semi-flush to the ceiling. **Maximum achievable height with stems included. Additional 12" stems available. For 3797 BN, use stem 4312 BN. For 3794 BN, use stem 6066 BN.

BLAKELY™

FINISH BUCKEYE BRONZE
SHADE DUNE HEATHERED LINEN

The Blakely collection defines soft modern elegance with a sleek intersecting outer frame that seamlessly encloses a sophisticated heathered fabric drum shade.

ADDITIONAL FINISHES
Brushed Nickel (BN)



3796 KZ
22" DIA., 35½" H



3797 KZ
12" DIA., 16" H
60½" MAX. H**



3794 KZ
24" DIA., 12½" H
55¼" MAX. H**
includes bottom acrylic lens



3794 KZ
24" DIA., 15¼" H*
includes bottom acrylic lens
(mounted as semi-flush)



3793 KZ
16½" DIA., 27" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN	STEMS INCLUDED
3793 KZ	3-60w Cand.	5½" Dia.	12', 10'	
3794 KZ	4-100w Med.	5½" Dia.	10' Wire	1-4", 1-6", 1-12", 1-18"
3796 KZ	4-100w Med.	5½" Dia.	12', 10'	
3797 KZ	1-100w Med.	5½" Dia.	12' Wire	1-6", 3-12"

*Minimum height when mounting semi-flush to the ceiling. **Maximum achievable height with stems included. Additional 12" stems available. For 3797 KZ, use stem 4312 KZ. For 3794 KZ, use stem 6066 KZ.

HAMPTON™

FINISH ANTIQUE NICKEL
SHADE OFF-WHITE LINEN HARDBACK

Hampton is a modern transitional design, offering the ultimate in urban sophistication. The minimal, rectangular frame, paired with a decorative acrylic etched bottom lens, is softened by a contemporary off-white linen drum shade.

ADDITIONAL FINISHES

Brushed Bronze (BR), Buckeye Bronze (KZ)



3206 AN
3206 AN-LED
30" DIA., 33" H





3201 AN
3201 AN-LED
20" DIA., 12" H



3211 AN
3211 AN-LED
26" DIA., 14½" H



3200 AN
3200 AN-LED
15" DIA., 11¼" H



3203 AN
3203 AN-LED
20" DIA., 26½" H



3204 AN
3204 AN-LED
26" DIA., 30¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE/ CHAIN
3200 AN	3-60w Med.	3200 AN-LED	48w LED	2850	2700	96	3-100w	10" Dia.	
3201 AN	3-75w Med.	3201 AN-LED	48w LED	2850	2700	96	3-100w	12" Dia.	
3203 AN	3-60w Med.	3203 AN-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 5'
3204 AN	3-100w Med.	3204 AN-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 5'
3206 AN	3-100w Med.	3206 AN-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 10'
3211 AN	3-100w Med.	3211 AN-LED	48w LED	2850	2700	96	3-100w	15¾" Dia.	


For complete product details and LED specifications, refer to hinkleylighting.com.



3202 AN
15" W, 12" H



3210 AN
6¾" W, 12" H



3207 AN
3207 AN-LED
7" DIA., 11¼" H
44¼" MAX. H*
T24



3214 AN
29" DIA., 24" H



3209 AN
24¾" DIA., 24½" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	STEMS INCLUDED
3202 AN	2-60w Cand.							5½"	4¼"	4¾" W, 12" H Back Plate		
3207 AN	1-100w Med.	3207 AN-LED	15w LED	900	2700	90	1-75w			5" Dia. Canopy	10' Wire	1-6", 2-12"
3209 AN	4-100w Med.									5" Dia. Canopy	12', 10'	
3210 AN	1-100w Med.							8¼"	6"	4¾" W, 12" H Back Plate		
3214 AN	4-100w Med.									5" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 AN. For complete product details and LED specifications, refer to hinkleylighting.com.





3205 AN
16" DIA., 32¾" H



3217 AN
3217 AN-LED
9¼" DIA., 22½" H
 



3212 AN
3212 AN-LED
12¼" DIA., 29¾" H
 



3208 AN
40" W, 31¼" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	DEPTH	CANOPY	WIRE/CHAIN
3205 AN	3-60w Med.								5" Dia.	12', 10'
3208 AN	4-100w Med.							18"	4½" W, 7¼" L	12', 5'
3212 AN	4-60w Cand.	3212 AN-LED	30w LED	1800	2700	90	2-75w		5" Dia.	12', 10'
3217 AN	1-100w Med.	3217 AN-LED	15w LED	900	2700	90	1-75w		5" Dia.	12', 10'

For complete product details and LED specifications, refer to hinkleylighting.com.

HAMPTON™

FINISH BRUSHED BRONZE
SHADE OFF-WHITE LINEN HARDBACK

Hampton is a modern transitional design, offering the ultimate in urban sophistication. The minimal, rectangular frame, paired with a decorative acrylic etched bottom lens, is softened by a contemporary off-white linen drum shade.

ADDITIONAL FINISHES

Antique Nickel (AN), Buckeye Bronze (KZ)

— @INSTAFAVE —



@studio_o_interiors

THE HAMPTON COLLECTION



3206 BR
3206 BR-LED
30" DIA., 33" H





3201 BR
3201 BR-LED
20" DIA., 12" H



3211 BR
3211 BR-LED
26" DIA., 14½" H



3200 BR
3200 BR-LED
15" DIA., 11¾" H



3203 BR
3203 BR-LED
20" DIA., 26½" H



3204 BR
3204 BR-LED
26" DIA., 30¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE/ CHAIN
3200 BR	3-60w Med.	3200 BR-LED	48w LED	2850	2700	96	3-100w	10" Dia.	
3201 BR	3-75w Med.	3201 BR-LED	48w LED	2850	2700	96	3-100w	12" Dia.	
3203 BR	3-60w Med.	3203 BR-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 5'
3204 BR	3-100w Med.	3204 BR-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 5'
3206 BR	3-100w Med.	3206 BR-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 10'
3211 BR	3-100w Med.	3211 BR-LED	48w LED	2850	2700	96	3-100w	15¾" Dia.	

For complete product details and LED specifications, refer to hinkleylighting.com.



3202 BR
15" W, 12" H



3210 BR
6¾" W, 12" H



3207 BR
3207 BR-LED
7" DIA., 11¾" H
44¼" MAX. H*
T24



3214 BR
29" DIA., 24" H



3209 BR
24¾" DIA., 24½" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	STEMS INCLUDED
3202 BR	2-60w Cand.							5½"	4¼"	4¾" W, 12" H Back Plate		
3207 BR	1-100w Med.	3207 BR-LED	15w LED	900	2700	90	1-75w			5" Dia. Canopy	10' Wire	1-6", 2-12"
3209 BR	4-100w Med.									5" Dia. Canopy	12', 10'	
3210 BR	1-100w Med.							8¼"	6"	4¾" W, 12" H Back Plate		
3214 BR	4-100w Med.									5" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BR. For complete product details and LED specifications, refer to hinkleylighting.com.





3205 BR
16" DIA., 32¾" H



3217 BR
3217 BR-LED
9¼" DIA., 22½" H
 



3212 BR
3212 BR-LED
12¼" DIA., 29¾" H
 



3208 BR
40" W, 31¼" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	DEPTH	CANOPY	WIRE/CHAIN
3205 BR	3-60w Med.								5" Dia.	12', 10'
3208 BR	4-100w Med.							18"	4½" W, 7¼" L	12', 5'
3212 BR	4-60w Cand.	3212 BR-LED	30w LED	1800	2700	90	2-75w		5" Dia.	12', 10'
3217 BR	1-100w Med.	3217 BR-LED	15w LED	900	2700	90	1-75w		5" Dia.	12', 10'

For complete product details and LED specifications, refer to hinkleylighting.com.

HAMPTON™

FINISH BUCKEYE BRONZE
SHADE OFF-WHITE LINEN HARDBACK

Hampton is a modern transitional design, offering the ultimate in urban sophistication. The minimal, rectangular frame, paired with a decorative acrylic etched bottom lens, is softened by a contemporary off-white linen drum shade.

ADDITIONAL FINISHES

Antique Nickel (AN), Brushed Bronze (BR)



3206 KZ
3206 KZ-LED
30" DIA., 33" H





3201 KZ
3201 KZ-LED
20" DIA., 12" H



3211 KZ
3211 KZ-LED
26" DIA., 14½" H



3200 KZ
3200 KZ-LED
15" DIA., 11¾" H



3203 KZ
3203 KZ-LED
20" DIA., 26½" H



3204 KZ
3204 KZ-LED
26" DIA., 30¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE/ CHAIN
3200 KZ	3-60w Med.	3200 KZ-LED	48w LED	2850	2700	96	3-100w	10" Dia.	
3201 KZ	3-75w Med.	3201 KZ-LED	48w LED	2850	2700	96	3-100w	12" Dia.	
3203 KZ	3-60w Med.	3203 KZ-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 5'
3204 KZ	3-100w Med.	3204 KZ-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 5'
3206 KZ	3-100w Med.	3206 KZ-LED	48w LED	2850	2700	96	3-100w	5" Dia.	12', 10'
3211 KZ	3-100w Med.	3211 KZ-LED	48w LED	2850	2700	96	3-100w	15¾" Dia.	

For complete product details and LED specifications, refer to hinkleylighting.com.



3202 KZ
15" W, 12" H



3210 KZ
6¾" W, 12" H



3207 KZ
3207 KZ-LED
7" DIA., 11¾" H
44¼" MAX. H*



3214 KZ
29" DIA., 24" H



3209 KZ
24¾" DIA., 24½" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN	STEMS INCLUDED
3202 KZ	2-60w Cand.							5½"	4¼"	4¾" W, 12" H Back Plate		
3207 KZ	1-100w Med.	3207 KZ-LED	15w LED	900	2700	90	1-75w			5" Dia. Canopy	10' Wire	1-6", 2-12"
3209 KZ	4-100w Med.									5" Dia. Canopy	12', 10'	
3210 KZ	1-100w Med.							8¼"	6"	4¾" W, 12" H Back Plate		
3214 KZ	4-100w Med.									5" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 KZ. For complete product details and LED specifications, refer to hinkleylighting.com.





3205 KZ
16" DIA., 32¾" H



3217 KZ
3217 KZ-LED
9¼" DIA., 22½" H
 



3212 KZ
3212 KZ-LED
12¼" DIA., 29¾" H
 



3208 KZ
40" W, 31¼" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	DEPTH	CANOPY	WIRE/ CHAIN
3205 KZ	3-60w Med.								5" Dia.	12', 10'
3208 KZ	4-100w Med.							18"	4½" W, 7¼" L	12', 5'
3212 KZ	4-60w Cand.	3212 KZ-LED	30w LED	1800	2700	90	2-75w		5" Dia.	12', 10'
3217 KZ	1-100w Med.	3217 KZ-LED	15w LED	900	2700	90	1-75w		5" Dia.	12', 10'

For complete product details and LED specifications, refer to hinkleylighting.com.

HARRISON™

FINISH BUCKEYE BRONZE
SHADE OFF-WHITE LINEN

Harrison's transitional style creates a chic, minimalist silhouette with an edge of urban sophistication. The drum shade offers shadow-less construction and is accentuated by a bold metal ring with cast knob accents supporting an etched acrylic lens providing even and warm light throughout. This clean and current design offers enormous flexibility, adding a fresh appearance to a variety of environments, rooms and décor styles.



3705 KZ
26" DIA., 22" H
55" MAX. H*



3704 KZ
20" DIA., 19½" H
52½" MAX. H*



3701 KZ
15" DIA., 6½" H



3703 KZ
20" DIA., 10¼" H



3700 KZ
7" W, 11½" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3700 KZ	1-60w Cand.	4"	8¼"	5" Dia. Back Plate		
3701 KZ	3-60w Med.			12" Dia. Canopy		
3703 KZ	3-100w Med.			5¾" Dia. Canopy		
3704 KZ	3-100w Med.			5¼" Dia. Canopy	10'	1-6", 2-12"
3705 KZ	3-100w Med.			5¼" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6066 KZ.

CHARLOTTE™

FINISH BRUSHED CARAMEL
 GLASS ETCHED OPAL
 SHADE WOVEN OFF-WHITE FABRIC

Charlotte is an updated traditional design featuring a richly textured off-white fabric shade captured by wide solid metal uprights and trim rings. The domed bottom diffuser is captured inside a heavy trim ring and held by cast decorative knobs for a refined vintage touch.

ADDITIONAL FINISHES

Antique Nickel (AN), Chrome (CM)



3522 BC
 20" DIA., 13½" H



3521 BC
 16" DIA., 13" H



3523 BC
 16" DIA., 19½" H
 68¼" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3521 BC	3-75w Med.	5½" Dia.		
3522 BC	3-100w Med.	7" Dia.		
3523 BC	3-75w Med.	5" Dia.	10'	1-4", 1-6", 1-12", 1-24"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BC.

Charlotte is an updated traditional design featuring a richly textured off-white fabric shade captured by wide solid metal uprights and trim rings. The domed bottom diffuser is captured inside a heavy trim ring and held by cast decorative knobs for a refined vintage touch.

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL
SHADE WOVEN OFF-WHITE FABRIC

CHARLOTTE™

ADDITIONAL FINISHES
Brushed Caramel (BC), Chrome (CM)



3523 AN
16" DIA., 19½" H
68¼" MAX. H*



3522 AN
20" DIA., 13½" H



3521 AN
16" DIA., 13" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
3521 AN	3-75w Med.	5½" Dia.		
3522 AN	3-100w Med.	7" Dia.		
3523 AN	3-75w Med.	5" Dia.	10'	1-4", 1-6", 1-12", 1-24"

*Maximum achievable height with stems included. Additional 12" stems available, 6068 AN.

CHARLOTTE™

FINISH CHROME
 GLASS ETCHED OPAL
 SHADE WOVEN OFF-WHITE FABRIC

Charlotte is an updated traditional design featuring a richly textured off-white fabric shade captured by wide solid metal uprights and trim rings. The domed bottom diffuser is captured inside a heavy trim ring and held by cast decorative knobs for a refined vintage touch.

ADDITIONAL FINISHES

Antique Nickel (AN), Brushed Caramel (BC)



3522 CM
 20" DIA., 13½" H



3521 CM
 16" DIA., 13" H



3523 CM
 16" DIA., 19½" H
 68¼" MAX. H*

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED
3521 CM	3-75w Med.	5½" Dia.		
3522 CM	3-100w Med.	7" Dia.		
3523 CM	3-75w Med.	5" Dia.	10'	1-4", 1-6", 1-12", 1-24"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 CM.



RE-IMAGINE RECESSED LIGHTING


WITH AN EASY DECORATIVE UPGRADE

Recessed lighting is a familiar feature throughout many homes. It provides directional light on opposing surfaces, such as countertops and floors. The illumination provided from recessed lights often falls short in providing adequate light across the walls and ceiling. Spaces such as hallways, entryways, kitchens, bathrooms and closets can benefit from the stylish touch of a flush mount, casting light evenly throughout the entire space. Consider replacing existing recessed can lights with ceiling mounted fixtures to update your décor while providing better overall ambient lighting. With the QuickFit recessed light converter kit, it's as easy as 1-2-3! Pencil in this simple project as your next quick weekend task—no remodeling required!

LEFT: THE HADLEY + HARPER COLLECTIONS
3300CM, PAGE 308 AND 3641CM, PAGE 315

THE QUICKFIT KIT

80100 QF QUICKFIT RECESSED LIGHT CONVERTER KIT



STEP 1: Mount QuickFit adjustable bar and screw in socket adapter.



STEP 2: Mount fixture hardware and fixture mounting screws to QuickFit bar.



STEP 3: Wire fixture to socket adapter. Secure fixture with hardware.

ITEM	SOCKET ADAPTER	FITS CAN SIZE	EXCLUDED CAN TYPES	MAX WEIGHT	MOUNTING STRAP TYPE
80100 QF	Medium Base	4" - 6"	Pop-in	50 lbs.	Any



LOOK FOR THE QUICKFIT ICON TO FIND FIXTURES THAT CAN BE ORDERED WITH THE QUICKFIT KIT. ALSO AVAILABLE SEPARATELY, 80100 QF.



HATHAWAY 32280B-WH-QF
PAGE 187



HADLEY 3308BR-QF,
PAGE 309

HATHAWAY™

FINISH OLDE BRONZE
GLASS ETCHED

Hathaway's striking design features a bold shade held in place by three intersecting, floating arms with unique forged uprights and ring detail for a modern style. Available in Antique Nickel with etched glass, Olde Bronze with etched glass and Olde Bronze with etched amber glass.

ADDITIONAL FINISHES

Antique Nickel (AN),
Olde Bronze with Amber Glass (OB)



3224 OB-WH
3224 OB-WH-LED
26³/₄" DIA., 29¹/₄" H
61³/₄" MAX. H*





3225 OB-WH
3225 OB-WH-LED
16" DIA., 5¼" H
T24



3226 OB-WH
3226 OB-WH-LED
21¼" DIA., 6¼" H
T24



3223 OB-WH
3223 OB-WH-LED
13" DIA., 4½" H
T24



3221 OB-WH
3221 OB-WH-LED
20¾" DIA., 12¼" H
T24



3222 OB-WH
3222 OB-WH-LED
20¾" DIA., 26½" H
59" MAX. H*
T24



3220 OB-WH
3220 OB-WH-LED
16" DIA., 11¾" H
T24



3228 OB-WH
3228 OB-WH-QF**
7" DIA., 3¼" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE	STEMS INCLUDED
3220 OB-WH	3-100w Med.	3220 OB-WH-LED	32w LED	1900	2700K	96	2-100w	5¾" Dia.		
3221 OB-WH	4-100w Med.	3221 OB-WH-LED	48w LED	2850	2700K	96	3-100w	5¾" Dia.		
3222 OB-WH	4-100w Med.	3222 OB-WH-LED	48w LED	2850	2700K	96	3-100w	5" Dia.	10'	1-6", 2-12"
3223 OB-WH	2-60w Med.	3223 OB-WH-LED	16w LED	950	2700K	96	1-100w	12" Dia.		
3224 OB-WH	5-100w Med.	3224 OB-WH-LED	64w LED	3800	2700K	96	4-100w	5" Dia.	10'	1-6", 2-12"
3225 OB-WH	3-60w Med.	3225 OB-WH-LED	32w LED	1900	2700K	96	2-100w	15¼" Dia.		
3226 OB-WH	4-60w Med.	3226 OB-WH-LED	48w LED	2850	2700K	96	3-100w	20½" Dia.		
		3228 OB-WH	16w LED	930	2700K	96	1-100w	6¼" Dia.		
		3228-OB-WH-QF**	16w LED	930	2700K	96	1-100w	6¼" Dia.		

*Maximum achievable height with stems included. Additional 12" stems available. For 3222 OB-WH use 4512 OB, and for 3224 OB-WH use 6066 OB.
 **3228 OB-WH-QF includes QuickFit recessed light converter kit, 80100 QF, also available separately. See page 185. 3228 OB-WH flush mount is ADA compliant when mounted as a sconce. For complete product details and LED specifications, refer to hinkleylighting.com.

HATHAWAY™

FINISH OLDE BRONZE
GLASS ETCHED AMBER

Hathaway's striking design features a bold shade held in place by three intersecting, floating arms with unique forged uprights and ring detail for a modern style. Available in Antique Nickel with etched glass, Olde Bronze with etched glass and Olde Bronze with etched amber glass.

ADDITIONAL FINISHES



Antique Nickel (AN),
Olde Bronze with Etched Glass (OB-WH)





3224 OB
3224 OB-LED
26¾" DIA., 29¼" H
61¾" MAX. H*







3225 OB
3225 OB-LED
16" DIA., 5¼" H
 





3226 OB
3226 OB-LED
21¼" DIA., 6¼" H
 






3223 OB
3223 OB-LED
13" DIA., 4½" H
 



3221 OB
3221 OB-LED
20¾" DIA., 12¼" H
 






3222 OB
3222 OB-LED
20¾" DIA., 26½" H
59½" MAX. H*
  



3220 OB
3220 OB-LED
16" DIA., 11¾" H
 



3228 OB
3228 OB-QF**
7" DIA., 3¼" H
  

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE	STEMS INCLUDED
3220 OB	3-100w Med.	3220 OB-LED	32w LED	1900	2700K	96	2-100w	5¾" Dia.		
3221 OB	4-100w Med.	3221 OB-LED	48w LED	2850	2700K	96	3-100w	5¾" Dia.		
3222 OB	4-100w Med.	3222 OB-LED	48w LED	2850	2700K	96	3-100w	5" Dia.	10'	1-6", 2-12"
3223 OB	2-60w Med.	3223 OB-LED	16w LED	950	2700K	96	1-100w	12" Dia.		
3224 OB	5-100w Med.	3224 OB-LED	64w LED	3800	2700K	96	4-100w	5" Dia.	10'	1-6", 2-12"
3225 OB	3-60w Med.	3225 OB-LED	32w LED	1900	2700K	96	2-100w	15¼" Dia.		
3226 OB	4-60w Med.	3226 OB-LED	48w LED	2850	2700K	96	3-100w	20½" Dia.		
		3228 OB	16w LED	930	2700K	96	1-100w	6¼" Dia.		
		3228-OB-QF**	16w LED	930	2700K	96	1-100w	6¼" Dia.		

*Maximum achievable height with stems included. Additional 12" stems available. For 3222 OB use 4512 OB, and for 3224 OB use 6066 OB.
 **3228 OB-QF includes QuickFit recessed light converter kit, 80100 QF, also available separately. See page 185. 3228 OB flush mount is ADA compliant when mounted as a sconce. For complete product details and LED specifications, refer to hinkleylighting.com.

HATHAWAY™

FINISH ANTIQUE NICKEL
GLASS ETCHED

Hathaway's striking design features a bold shade held in place by three intersecting, floating arms with unique forged uprights and ring detail for a modern style. Available in Antique Nickel with etched glass, Olde Bronze with etched glass and Olde Bronze with etched amber glass.

ADDITIONAL FINISHES

Olde Bronze with Amber Glass (OB),
Olde Bronze with Etched Glass (OB-WH)



3224 AN
3224 AN-LED
26¾" DIA., 29¼" H
61¾" MAX. H*





3225 AN
3225 AN-LED
16" DIA., 5¼" H



3226 AN
3226 AN-LED
21¼" DIA., 6¼" H



3223 AN
3223 AN-LED
13" DIA., 4½" H



3221 AN
3221 AN-LED
20¾" DIA., 12¼" H



3222 AN
3222 AN-LED
20¾" DIA., 26½" H
59½" MAX. H*



3220 AN
3220 AN-LED
16" DIA., 11¾" H



3228 AN
7" DIA., 3¼" H
(shown mounted as a sconce)



3228 AN
3228 AN-QF**
7" DIA., 3¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE	STEMS INCLUDED
3220 AN	3-100w Med.	3220 AN-LED	32w LED	1900	2700K	96	2-100w	5¾" Dia.		
3221 AN	4-100w Med.	3221 AN-LED	48w LED	2850	2700K	96	3-100w	5¾" Dia.		
3222 AN	4-100w Med.	3222 AN-LED	48w LED	2850	2700K	96	3-100w	5" Dia.	10'	1-6", 2-12"
3223 AN	2-60w Med.	3223 AN-LED	16w LED	950	2700K	96	1-100w	12" Dia.		
3224 AN	5-100w Med.	3224 AN-LED	64w LED	3800	2700K	96	4-100w	5" Dia.	10'	1-6", 2-12"
3225 AN	3-60w Med.	3225 AN-LED	32w LED	1900	2700K	96	2-100w	15¼" Dia.		
3226 AN	4-60w Med.	3226 AN-LED	48w LED	2850	2700K	96	3-100w	20½" Dia.		
		3228 AN	16w LED	930	2700K	96	1-100w	6¼" Dia.		
		3228-AN-QF**	16w LED	930	2700K	96	1-100w	6¼" Dia.		

*Maximum achievable height with stems included. Additional 12" stems available, 4512 AN. **3228 AN-QF includes QuickFit recessed light converter kit, 80100 QF, also available separately. See page 185. 3228 AN flush mount is ADA compliant when mounted as a sconce. For complete product details and LED specifications, refer to hinkleylighting.com.



Meridian features minimal transitional styling with clean lines, soft curves and low-profile faceted ½ thick glass. This stem hung simplistic design will add a crisp focal point to any décor.

Meridian Bath, pages 364-365

FINISH BRUSHED NICKEL
GLASS THICK FACETED
CLEAR INSIDE ETCHED

MERIDIAN™



3878 BN
34" DIA., 27" H



3873 BN
24" DIA., 18½" H
5¼" MAX. H*



3875 BN
27" DIA., 18½" H
5¼" MAX. H*



3876 BN
34" DIA., 46¼" H



ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN	STEMS INCLUDED
3873 BN	3-60w G9**	5½" Dia.	10' Wire	1-6", 2-12"
3875 BN	5-60w G9**	5½" Dia.	10' Wire	1-6", 2-12"
3876 BN	12-60w G9**	5½" Dia.	10', 5'	
3878 BN	9-60w G9**	5½" Dia.	10', 5'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4512 BN. For 3877 BN, use 4312 BN. **G9 halogen bulbs included.



3871 BN
16" DIA., 12¼" H



5590 BN
5590 BN-LED
5" W, 8" H



3870 BN
5" W, 11¼" H



3872 BN
20" DIA., 23" H
55" MAX H.*



3877 BN
7½" DIA., 4¼" H
36¾" MAX. H*



3874 BN
44" W, 20" H
52¾" MAX. H*

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3870 BN	1-60w G9**				6½"	4"	4½" W, 8" H Back Plate		
3871 BN	3-60w G9**						5½" Dia. Canopy		
3872 BN	3-100w Med.						5½" Dia. Canopy	10'	1-6", 2-12"
3874 BN	4-60w G9**			7½"			5½" Dia. Canopy	10'	1-6", 2-12"
3877 BN	1-60w G9**						6" Dia. Canopy	10'	1-6", 2-12"
5590 BN	1-60w G9**	5590 BN-LED	1-4.5w G9 LED***		6½"	4"	4½" W, 8" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 4512 BN. For 3877 BN, use 4312 BN. **G9 halogen bulbs included. ***G9 LED bulbs included. For complete product details and LED specifications, refer to hinkleylighting.com.

MIDTOWN™

FINISH BRUSHED NICKEL
GLASS MULTI-FACETED ETCHED

Midtown's clean, transitional design features an over scaled center column in Brushed Nickel with a faceted ribbed pattern on the etched glass.



4978 BN
32" DIA., 29" H



4970 BN
5" W, 8" H



4971 BN
18" DIA., 11¼" H



4975 BN
24" DIA., 22¼" H



4972 BN
18" DIA., 19½" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4970 BN	1-100w Med.	6¼"	4"	5" W, 8" H Back Plate	
4971 BN	3-100w Med.			6" Dia. Canopy	
4972 BN	3-100w Med.			6" Dia. Canopy	12', 10'
4975 BN	5-100w Med.			6" Dia. Canopy	6', 5'
4978 BN	9-100w Med.			6" Dia. Canopy	12', 10'

LATITUDE™

FINISH BRUSHED NICKEL
GLASS CLEAR INSIDE ETCHED

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the Brushed Nickel frame adds understated architectural style.

Latitude Bath, pages 339-341

ADDITIONAL FINISHES


Oil Rubbed Bronze (OZ)



3992 BN
8" W, 16" H



5651 BN
5½" W, 21½" H



3996 BN
42" W, 8½" H
49½" MAX. H*



3997 BN
8" W, 16½" H
55" MAX. H*



ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3992 BN	2-60w Cand.		4"	7¾"	8" W, 15½" H Back Plate		
3996 BN	4-100w Med.	8"			4½" W, 9¼" L Canopy	10'	4-6", 4-12"
3997 BN	2-100w Med.				4¾" Dia. Canopy	10'	2-6", 2-12"
5651 BN**	2-100w Med.		5½"	10¾"	5½" W, 21½" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available. For 3996 BN use 6068 BN, and for 3997 BN use FR84312BNI.

**Also available in Chrome (CM) and Oil Rubbed Bronze (OZ)

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the Oil Rubbed Bronze frame adds understated architectural style.

Latitude Bath, pages 339-341

FINISH OIL RUBBED BRONZE
GLASS CLEAR INSIDE ETCHED

LATITUDE™

ADDITIONAL FINISHES
Brushed Nickel (BN)



3997 OZ
8" W, 16½" H
55" MAX. H*



5651 OZ
5½" W, 21½" H



3992 OZ
8" W, 16" H



3996 OZ
42" W, 8½" H, 8" D
49½" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3992 OZ	2-60w Cand.		4"	7¾"	8" W, 15½" H Back Plate		
3996 OZ	4-100w Med.	8"			4½" W, 9¼" L Canopy	10'	4-6", 4-12"
3997 OZ	2-100w Med.				4¾" Dia. Canopy	10'	2-6", 2-12"
5651 OZ**	2-100w Med.		5½"	10¾"	5½" W, 21½" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available. For 3996 OZ use 6068 OZ, and for 3997 OZ use 4312 OZ.
**Also available in Brushed Nickel (BN) and Chrome (CM).

MONDRIAN™

FINISH BUCKEYE BRONZE
GLASS COPPER FOIL BOUND
GLASS PANELS

Mondrian's unique patterned panels of glass mounted in copper foil adds geometric panache in a Buckeye Bronze finish.



4576 KZ
14" SQ., 42" H



4572 KZ
7" W, 24" H
(sconce)



4570 KZ
7" W, 11" H
(sconce)



4571 KZ
16" SQ., 13½" H*



4571 KZ
(mounted as semi-flush)



4575 KZ
36" W, 24" H



4574 KZ
14" SQ., 26" H



4577 KZ
7" SQ., 11" H
43¾" MAX. H**

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
4570 KZ	2-60w Cand.	4"	5½"	7" W, 10½" H Back Plate		
4571 KZ	4-60w Cand.			7" Sq. Canopy	6', 5'	
4572 KZ	3-60w Cand.	4"	12"	7" W, 23" H Back Plate		
4574 KZ	4-60w Cand.			7" Sq. Canopy	6', 5'	
4575 KZ	5-60w Cand.			4½" W, 21¼" L Canopy	6', 5'	
4576 KZ	12-60w Cand.			7" Sq. Canopy	12', 10'	
4577 KZ	1-100w Med.			5" Sq. Canopy	10' Wire	1-6", 2-12"

*Height when hung with chain. When mounted as semi-flush, height is 12". **Maximum achievable height with stems included. Additional 12" stems available, 4312 KZ.

BOLLA™

FINISH BRUSHED BRONZE
GLASS LIGHT AMBER SEEDY

The graceful lines of Bolla's sweeping double arms create a soft elegance while heavy cast spheres perched at the tips add to its innovative style. The strong proportions of the arms contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Bath, pages 386-390

ADDITIONAL FINISHES

Brushed Nickel with Etched Opal Glass (BN),
Olde Bronze with Clear Seedy Glass (OB-CL),
Olde Bronze with Etched Opal Glass (OB-OPAL),
Olde Bronze with Light Amber Seedy Glass (OB)



4657 BR
35¼" DIA., 37½" H



4652 BR
23¼" DIA., 26¼" H



4669 BR
4669 BR-LED
23¼" DIA., 16" H
T24



4650 BR
7¾" W, 8½" H



4651 BR
4651 BR-LED
19¼" DIA., 14¼" H
T24



4667 BR
7¾" DIA., 7¼" H
39½" MAX. H*



4653 BR
22½" DIA., 18¼" H



4656 BR
29" DIA., 29" H



4655 BR
24" DIA., 24" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TTO	BACK PLATE/ CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4650 BR	1-100w Med.							8¾"	3½"	6" W, 7½" H Back Plate		
4651 BR	2-100w Med.	4651 BR-LED	32w LED	1900	2700K	96	2-100w			6" Dia. Canopy		
4652 BR	3-100w Med.									6" Dia. Canopy	6', 5'	
4653 BR	3-100w Med.									6" Dia. Canopy	6', 5'	
4655 BR	5-100w Med.									6" Dia. Canopy	6', 5'	
4656 BR	6-100w Med.									6" Dia. Canopy	6', 5'	
4657 BR	9-100w Med.									6" Dia. Canopy	12', 10'	
4667 BR	1-100w Med.									5½" Dia. Canopy	10' Wire	1-6", 2-12"
4669 BR	3-100w Med.	4669 BR-LED	48w LED	2850	2700K	96	3-100w			6" Dia. Canopy		

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BR. For complete product details and LED specifications, refer to hinkleylighting.com.

BOLLA™

FINISH OLDE BRONZE
GLASS CLEAR SEEDY

The graceful lines of Bolla's sweeping double arms create a soft elegance while heavy cast spheres perched at the tips add to its innovative style. The strong proportions of the arms contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Bath, pages 386-390

ADDITIONAL FINISHES

Brushed Bronze with Light Amber Seedy Glass (BR),
Brushed Nickel with Etched Opal Glass (BN),
Olde Bronze with Etched Opal Glass (OB-OPAL),
Olde Bronze with Light Amber Seedy Glass (OB)



4659 OB-CL
48" DIA., 48½" H

50




4655 OB-CL
24" DIA., 24" H



4667 OB-CL
7¾" DIA., 7¼" H
39½" MAX. H*



4653 OB-CL
22½" DIA., 18¼" H



4661 OB-CL
15½" DIA., 8¼" H
48" MAX. H*



4656 OB-CL
29" DIA., 29" H



4657 OB-CL
35¼" DIA., 37½" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4653 OB-CL	3-100w Med.	6" Dia.	6', 5'	
4655 OB-CL	5-100w Med.	6" Dia.	6', 5'	
4656 OB-CL	6-100w Med.	6" Dia.	6', 5'	
4657 OB-CL	9-100w Med.	6" Dia.	12', 10'	
4659 OB-CL	18-60w Med.	6" Dia.	12', 10'	
4661 OB-CL	1-100w Med.	6" Dia.	10', 5'	3-12"
4667 OB-CL	1-100w Med.	5½" Dia.	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 OB.



4650 OB-CL
7¾" W, 8½" H



4666 OB-CL
56" W, 25¼" H



4671 OB-CL
8" W, 26" H



4662 OB-CL
44¼" W, 26½" H



4663 OB-CL
16" DIA., 29" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
4650 OB-CL	1-100w Med.		8¾"	3½"	6" W, 7½" H Back Plate	
4662 OB-CL	2-100w Med.	15½"			6" Dia. Canopy	6', 5'
4663 OB-CL	3-60w Cand.				6" Dia. Canopy	6', 5'
4666 OB-CL	3-100w Med.	15½"			6" Dia. Canopy	6', 5'
4671 OB-CL	1-100w Med.		9"	7½"	6" Dia. Back Plate	



4660 OB-CL
16¾" DIA., 8" H



4651 OB-CL
19¼" DIA., 14¼" H



4669 OB-CL
23¼" DIA., 16" H



4652 OB-CL
23½" DIA., 26¼" H



4665 OB-CL
18" DIA., 44" H



4664 OB-CL
30" DIA., 32" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN
4651 OB-CL	2-100w Med.	6" Dia.	
4652 OB-CL	3-100w Med.	6" Dia.	6', 5'
4660 OB-CL	2-75w Med.	5" Dia.	
4664 OB-CL	4-75w Med.	6¼" Dia.	12', 10'
4665 OB-CL	6-60w Cand.	6¼" Dia.	12', 10'
4669 OB-CL	3-100w Med.	6" Dia.	

BOLLA™

FINISH OLDE BRONZE
GLASS ETCHED OPAL

The graceful lines of Bolla's sweeping double arms create a soft elegance while heavy cast spheres perched at the tips add to its innovative style. The strong proportions of the arms contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Bath, pages 386-390

ADDITIONAL FINISHES

Brushed Bronze with Light Amber Seedy Glass (BR),
Brushed Nickel with Etched Opal Glass (BN),
Olde Bronze with Clear Seedy Glass (OB-CL),
Olde Bronze with Light Amber Seedy Glass (OB)



4659 OB-OPAL
48" DIA., 48½" H

50



4655 OB-OPAL
24" DIA., 24" H



4667 OB-OPAL
7¾" DIA., 7¼" H
39½" MAX. H*



4653 OB-OPAL
22½" DIA., 18¼" H



4661 OB-OPAL
15½" DIA., 8¼" H
48" MAX. H*



4656 OB-OPAL
29" DIA., 29" H



4657 OB-OPAL
35¼" DIA., 37½" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4653 OB-OPAL	3-100w Med.	6" Dia.	6', 5'	
4655 OB-OPAL	5-100w Med.	6" Dia.	6', 5'	
4656 OB-OPAL	6-100w Med.	6" Dia.	6', 5'	
4657 OB-OPAL	9-100w Med.	6" Dia.	12', 10'	
4659 OB-OPAL	18-60w Med.	6" Dia.	12', 10'	
4661 OB-OPAL	1-100w Med.	6" Dia.	10', 5'	3-12"
4667 OB-OPAL	1-100w Med.	5½" Dia.	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 OB.



4650 OB-OPAL
7¾" W, 8½" H



4671 OB-OPAL
8" W, 26" H



4666 OB-OPAL
56" W, 25¼" H



4662 OB-OPAL
44¼" W, 26½" H



4663 OB-OPAL
16" DIA., 29" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
4650 OB-OPAL	1-100w Med.		8¾"	3½"	6" W, 7½" H Back Plate	
4662 OB-OPAL	2-100w Med.	15½"			6" Dia. Canopy	6', 5'
4663 OB-OPAL	3-60w Cand.				6" Dia. Canopy	6', 5'
4666 OB-OPAL	3-100w Med.	15½"			6" Dia. Canopy	6', 5'
4671 OB-OPAL	1-100w Med.		9"	7½"	6" Dia. Back Plate	



4660 OB-OPAL
4660 OB-OP-LED
16¾" DIA., 8" H



4651 OB-OPAL
4651 OB-OP-LED
19¼" DIA., 14¼" H



4669 OB-OPAL
4669 OB-OP-LED
23¼" DIA., 16" H



4652 OB-OPAL
23½" DIA., 26¼" H



4665 OB-OPAL
18" DIA., 44" H



4664 OB-OPAL
30" DIA., 32" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE/CHAIN
4651 OB-OPAL	2-100w Med.	4651 OB-OP-LED	32w LED	1900	2700K	96	2-100w	6" Dia.	
4652 OB-OPAL	3-100w Med.							6" Dia.	6', 5'
4660 OB-OPAL	2-75w Med.	4660 OB-OP-LED	32w LED	1900	2700K	96	2-100w	5" Dia.	
4664 OB-OPAL	4-75w Med.							6¼" Dia.	12', 10'
4665 OB-OPAL	6-60w Cand.							6¼" Dia.	12', 10'
4669 OB-OPAL	3-100w Med.	4669 OB-OP-LED	48w LED	2850	2700K	96	3-100w	6" Dia.	

For complete product details and LED specifications, refer to hinkleylighting.com.

BOLLA™

FINISH OLDE BRONZE
GLASS LIGHT AMBER SEEDY

The graceful lines of Bolla's sweeping double arms create a soft elegance while heavy cast spheres perched at the tips add to its innovative style. The strong proportions of the arms contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Bath, pages 386-390

ADDITIONAL FINISHES

Brushed Bronze with Light Amber Seedy Glass (BR),
Brushed Nickel with Etched Opal Glass (BN),
Olde Bronze with Clear Seedy Glass (OB-CL),
Olde Bronze with Etched Opal Glass (OB-OPAL)



4659 OB
48" DIA., 48½" H





4655 OB
24" DIA., 24" H



4667 OB
7¾" DIA., 7¼" H
39½" MAX. H*



4653 OB
22½" DIA., 18" H



4661 OB
15½" DIA., 8¼" H
48" MAX. H*



4656 OB
29" DIA., 29" H



4657 OB
35¼" DIA., 37½" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4653 OB	3-100w Med.	6" Dia.	6', 5'	
4655 OB	5-100w Med.	6" Dia.	6', 5'	
4656 OB	6-100w Med.	6" Dia.	6', 5'	
4657 OB	9-100w Med.	6" Dia.	12', 10'	
4659 OB	18-60w Med.	6" Dia.	12', 10'	
4661 OB	1-100w Med.	6" Dia.	10', 5'	3-12"
4667 OB	1-100w Med.	5½" Dia.	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 OB.



4650 OB
7¾" W, 8½" H



4671 OB
8" W, 26" H



4666 OB
56" W, 25¼" H



4662 OB
44¼" W, 26½" H



4663 OB
16" DIA., 29" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
4650 OB	1-100w Med.		8¾"	3½"	6" W, 7½" H Back Plate	
4662 OB	2-100w Med.	15½"			6" Dia. Canopy	6', 5'
4663 OB	3-60w Cand.				6" Dia. Canopy	6', 5'
4666 OB	3-100w Med.	15½"			6" Dia. Canopy	6', 5'
4671 OB	1-100w Med.		9"	7½"	6" Dia. Back Plate	



4660 OB
4660 OB-LED
16¾" DIA., 8" H



4651 OB
4651 OB-LED
19¼" DIA., 14¼" H



4669 OB
4669 OB-LED
23¼" DIA., 16" H



4652 OB
23½" DIA., 26¼" H



4665 OB
18" DIA., 44" H



4664 OB
30" DIA., 32" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE/CHAIN
4651 OB	2-100w Med.	4651 OB-LED	32w LED	1900	2700K	96	2-100w	6" Dia.	
4652 OB	3-100w Med.							6" Dia.	6', 5'
4660 OB	2-75w Med.	4660 OB-LED	32w LED	1900	2700K	96	2-100w	5" Dia.	
4664 OB	4-75w Med.							6¼" Dia.	12', 10'
4665 OB	6-60w Cand.							6¼" Dia.	12', 10'
4669 OB	3-100w Med.	4669 OB-LED	48w LED	2850	2700K	96	3-100w	6" Dia.	

For complete product details and LED specifications, refer to hinkleylighting.com.

BOLLA™

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

The graceful lines of Bolla's sweeping double arms create a soft elegance while heavy cast spheres perched at the tips add to its innovative style. The strong proportions of the arms contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Bath, pages 386-390

ADDITIONAL FINISHES

Brushed Bronze with Light Amber Seedy Glass (BR),
Olde Bronze with Clear Seedy Glass (OB-CL),
Olde Bronze with Etched Opal Glass (OB-OPAL),
Olde Bronze with Light Amber Seedy Glass (OB)



4659 BN
48" DIA., 48½" H

50




4655 BN
24" DIA., 24" H



4667 BN
7¾" DIA., 7¼" H
39½" MAX. H*



4653 BN
22½" DIA., 18" H



4661 BN
15½" DIA., 8¼" H
48" MAX. H*



4656 BN
29" DIA., 29" H



4657 BN
35¼" DIA., 37½" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4653 BN	3-100w Med.	6" Dia.	6', 5'	
4655 BN	5-100w Med.	6" Dia.	6', 5'	
4656 BN	6-100w Med.	6" Dia.	6', 5'	
4657 BN	9-100w Med.	6" Dia.	12', 10'	
4659 BN	18-60w Med.	6" Dia.	12', 10'	
4661 BN	1-100w Med.	6" Dia.	10', 5'	3-12"
4667 BN	1-100w Med.	5½" Dia.	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BN.



4650 BN
7¾" W, 8½" H



4666 BN
56" W, 25¼" H



4671 BN
8" W, 26" H





4662 BN
44¼" W, 26½" H





4663 BN
16" DIA., 29" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
4650 BN	1-100w Med.		8¾"	3½"	6" W, 7½" H Back Plate	
4662 BN	2-100w Med.	15½"			6" Dia. Canopy	6', 5'
4663 BN	3-60w Cand.				6" Dia. Canopy	6', 5'
4666 BN	3-100w Med.	15½"			6" Dia. Canopy	6', 5'
4671 BN	1-100w Med.		9"	7½"	6" Dia. Back Plate	





4660 BN
4660 BN-LED
16¾" DIA., 8" H





4651 BN
4651 BN-LED
19¼" DIA., 14¼" H





4669 BN
4669 BN-LED
23¼" DIA., 16" H





4652 BN
23½" DIA., 26¼" H



4665 BN
18" DIA., 44" H



4664 BN
30" DIA., 32" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	CANOPY	WIRE/CHAIN
4651 BN	2-100w Med.	4651 BN-LED	32w LED	1900	2700K	96	2-100w	6" Dia.	
4652 BN	3-100w Med.							6" Dia.	6', 5'
4660 BN	2-75w Med.	4660 BN-LED	32w LED	1900	2700K	96	2-100w	5" Dia.	
4664 BN	4-75w Med.							6¼" Dia.	12', 10'
4665 BN	6-60w Cand.							6¼" Dia.	12', 10'
4669 BN	3-100w Med.	4669 BN-LED	48w LED	2850	2700K	96	3-100w	6" Dia.	

For complete product details and LED specifications, refer to hinkleylighting.com.

BRANTLEY™

FINISH BRUSHED NICKEL
GLASS ETCHED WHITE

Brantley's transitional design features bold arms that sweep outward, creating a striking effect, while geometric castings and decorative twin arm construction add to its beauty. The Brushed Nickel finish is complemented by etched white glass.

Brantley Bath, pages 414-415

ADDITIONAL FINISHES

Oil Rubbed Bronze (OZ-WH)



4639 BN
43" DIA., 34" H





4632 BN
17" DIA., 11" H



4631 BN
17" DIA., 7" H



4630 BN
4¾" W, 12¼" H



4637 BN
5" DIA., 9" H
47¼" MAX. H*



4638 BN
33¼" DIA., 32¾" H



4636 BN
30" DIA., 26½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
4630 BN	1-100w Med.	8½"	7"	4¾" W, 10" H Back Plate		
4631 BN	3-60w Med.					
4632 BN	3-100w Med.			6" Dia. Canopy		
4636 BN	6-100w Med.			6" Dia. Canopy	6', 5'	
4637 BN	1-100w Med.			6" Dia. Canopy	10' Wire	2-6", 2-12"
4638 BN	9-75w Med.			6" Dia. Canopy	12', 10'	
4639 BN	12-60w Med.			6" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 BN.

BRANTLEY™

FINISH OIL RUBBED BRONZE
GLASS ETCHED WHITE

Brantley's transitional design features bold arms that sweep outward, creating a striking effect, while geometric castings and decorative twin arm construction add to its beauty. The Oil Rubbed Bronze finish is complemented by etched white glass.

Brantley Bath, pages 414-415

ADDITIONAL FINISHES
Brushed Nickel (BN)



4639 OZ-WH
43" DIA., 34" H

50



4632 OZ-WH
17" DIA., 11" H



4631 OZ-WH
17" DIA., 7" H



4630 OZ-WH
4¾" W, 12¼" H



4637 OZ-WH
5" DIA., 9" H
47¼" MAX. H*



4638 OZ-WH
33¾" DIA., 32¾" H



4636 OZ-WH
30" DIA., 26½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
4630 OZ-WH	1-100w Med.	8½"	7"	4¾" W, 10" H Back Plate		
4631 OZ-WH	3-60w Med.					
4632 OZ-WH	3-100w Med.			6" Dia. Canopy		
4636 OZ-WH	6-100w Med.			6" Dia. Canopy	6', 5'	
4637 OZ-WH	1-100w Med.			6" Dia. Canopy	10' Wire	2-6", 2-12"
4638 OZ-WH	9-75w Med.			6" Dia. Canopy	12', 10'	
4639 OZ-WH	12-60w Med.			6" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 OZ.

TRUMAN™

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL

The traditional style of the Truman collection features boldly sloped arms that uniquely contrast with its elegant cast finials. The Antique Nickel finish highlights the beautiful etched opal glass shades.



4028 AN
30" DIA., 32¼" H



4021 AN
16" DIA., 12" H



4023 AN
20" DIA., 22¼" H



4020 AN
5¼" W, 13" H



4027 AN
5¼" DIA., 8¼" H
40¼" MAX. H*



4024 AN
21¼" DIA., 24¼" H



4025 AN
27" DIA., 26½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
4020 AN	1-100w Med.	7¾"	8¼"	4½" W, 9¼" H Back Plate		
4021 AN	3-100w Med.			6½" Dia. Canopy		
4023 AN	3-100w Med.			5¾" Dia. Canopy	6', 5'	
4024 AN	4-100w Med.			5¾" Dia. Canopy	6', 5'	
4025 AN	5-100w Med.			5¾" Dia. Canopy	6', 5'	
4027 AN	1-100w Med.			5¾" Dia. Canopy	10' Wire	1-6", 2-12"
4028 AN	9-100w Med.			5¾" Dia. Canopy	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 AN.

SABINA™

FINISH SILVER LEAF
GLASS ETCHED LENS
SHADE EGGHELL SILK

Sabina features an airy, linked geometric form in a glistening Silver Leaf finish that infuses a jewelry-like sheen to the design. An eggshell silk shade provides an elegant backdrop to the pattern while subtly masking the light source. A delicately ribbed canopy and finial enhances its luxe feel. The perfect mix of simplicity and complexity, Sabina defines sophistication.

Instagram logo @INSTAFAVE



@ashstinteriors

THE SABINA COLLECTION



4915 SL
28" DIA., 26" H



4911 SL
15" DIA., 7" H



4914 SL
22½" DIA., 12¼" H
4914 SL can be mounted in a close to ceiling position.



4916 SL
15" DIA., 26½" H
59½" MAX. H*



4913 SL
15" DIA., 14¾" H
47½" MAX. H*



4912 SL
11½" W, 16¾" H



4914 SL
22½" DIA., 7" H
39¾" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
4911 SL	3-60w Med.			12" Dia. Canopy		
4912 SL	2-60w Cand.	4"	10¾"	4¾" Square Back Plate		
4913 SL	3-60w Cand.			5½" Dia. Canopy	10' Wire	1-6", 2-12"
4914 SL	4-60w Med.			5½" Dia. Canopy	10' Wire	1-6", 2-12"
4915 SL	5-60w Cand.			5½" Dia. Canopy	12', 10'	
4916 SL	6-60w Cand.			5½" Dia. Canopy	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6063 SL.

MORGAN™

FINISH BRUSHED BRONZE
SHADE OFF-WHITE LINEN

Morgan is an updated traditional style that conveys both quality and comfort. The minimalist center hoop design creates a sense of openness. Elegant off-white linen shades trimmed in bronze silk combine with crystal ball accents and petite square arms for understated luxury.

ADDITIONAL FINISHES
Antique Nickel (AN)



4878 BR
35" DIA., 33½" H



4875 BR
27" DIA., 25" H



4870 BR
6" W, 12" H



4872 BR
6" W, 26" H



4876 BR
30" DIA., 27¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4870 BR	1-60w Cand.	7½"	7¼"	5" Dia. Back Plate	
4872 BR	1-60w Cand.	7"	10¾"	6" Dia. Back Plate	
4875 BR	5-60w Cand.			5¾" Dia. Canopy	6', 5'
4876 BR	6-60w Cand.			5¾" Dia. Canopy	6', 5'
4878 BR	9-60w Cand.			5¾" Dia. Canopy	12', 10'

MORGAN™

FINISH ANTIQUE NICKEL
SHADE WHITE LINEN

Morgan is an updated traditional style that conveys both quality and comfort. The minimalist center hoop design creates a sense of openness. Elegant white linen shades combine with crystal ball accents and petite square arms for understated luxury.

ADDITIONAL FINISHES
Brushed Bronze (BR)



4878 AN
35" DIA., 33½" H



4875 AN
27" DIA., 25" H



4870 AN
6" W, 12" H



4872 AN
6" W, 26" H



4876 AN
30" DIA., 27¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4870 AN	1-60w Cand.	7½"	7¼"	5" Dia. Back Plate	
4872 AN	1-60w Cand.	7"	10¾"	6" Dia. Back Plate	
4875 AN	5-60w Cand.			5¾" Dia. Canopy	6', 5'
4876 AN	6-60w Cand.			5¾" Dia. Canopy	6', 5'
4878 AN	9-60w Cand.			5¾" Dia. Canopy	12', 10'

SURREY™

FINISH POLISHED NICKEL
SHADE WHITE LINEN

Surrey combines traditional elegance and dazzling crystal details into a fresh, streamlined silhouette. Slim, tapered arms in Polished Nickel with faceted crystal bobeches surround a striking oblong center. Optional white fabric shades add a discreet layer of glamour.



4006 PN
26½" DIA., 32" H



4006 PN
28" DIA., 32" H
(shown with optional shades)



4002 PN
11¾" W, 15¼" H



4000 SH
5¾" DIA., 6" H
(optional shade)



4005 PN
24" DIA., 31¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4000 SH	Do not exceed 40w				
4002 PN	2-60w Cand.	6"	13¼"	4½" Square Back Plate	
4005 PN	5-60w Cand.			6" Dia. Canopy	12', 10'
4006 PN	6-60w Cand.			6" Dia. Canopy	12', 10'

WAVERLY™

FINISH WARM WHITE
WITH HERITAGE BRASS
SHADE LIGHT BEIGE (OPTIONAL)

Waverly is a modern update to the classical orb chandelier. A center crystal column anchors this stem-hung design while charming crystal accents and finials complement the clean lines of intersecting spheres in a bold finish. Light beige fabric shades provide an updated elegance, complementing the overall spherical form. Waverly imparts a sense of European sophistication paired with American sensibility.

ADDITIONAL FINISHES

Oil Rubbed Bronze (OZ)



4600 WT
10" W, 13" H



4605 WT
30" DIA., 34¾" H
67¾" MAX. H*



4604 WT
24" DIA., 28¾" H
61¾" MAX. H*



4600 SH
4½" DIA., 5" H
(optional shade)

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4600 SH	Do not exceed 40w					
4600 WT	1-60w Cand.	6½"	6¾"	6" Dia. Back Plate		
4604 WT	4-60w Cand.			5" Dia. Canopy	10'	1-6", 2-12"
4605 WT	5-60w Cand.			5" Dia. Canopy	10'	1-6", 2-12"

Additional 12" stems available. For 4604 WT, use 6037 HB. For 4605 WT, use 6067 HB.

Waverly is a modern update to the classical orb chandelier. A center crystal column anchors this stem-hung design while charming crystal accents and finials complement the clean lines of intersecting spheres in a bold finish. Light beige fabric shades provide an updated elegance, complementing the overall spherical form. Waverly imparts a sense of European sophistication paired with American sensibility.

FINISH OIL RUBBED BRONZE
SHADE LIGHT BEIGE (OPTIONAL)

WAVERLY™

ADDITIONAL FINISHES
Warm White with Heritage Brass (WT)



4604 OZ
24" DIA., 28¾" H
61¾" MAX. H*
(shown with optional shades)



4600 SH
4½" DIA., 5" H
(optional shade)



4605 OZ
30" DIA., 34¾" H
67¾" MAX. H*



4600 OZ
10" W, 13" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
4600 SH	Do not exceed 40w					
4600 OZ	1-60w Cand.	6½"	6¾"	6" Dia. Back Plate		
4604 OZ	4-60w Cand.			5" Dia. Canopy	10'	1-6", 2-12"
4605 OZ	5-60w Cand.			5" Dia. Canopy	10'	1-6", 2-12"

Additional 12" stems available. For 4604 OZ, use 6037 OZ. For 4605 OZ, use 6067 OZ.

CLARENDON™

FINISH AGED ZINC
WITH ANTIQUE NICKEL
GLASS CLEAR

Clarendon is a classic four sided foyer lantern group designed in an elegant two tone finish and constructed in forged iron with cast ball details and clear glass panels. Clarendon is updated tradition at its finest.

ADDITIONAL FINISHES

Bronze with Heritage Brass (BZ)



3413 DZ
8" W, 18¼" H



3415 DZ
12" W, 26½" H



3418 DZ
20" W, 44" H



3414 DZ
16" W, 33¾" H


ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3413 DZ	3-60w Cand.	5" Square	12', 10'
3414 DZ	6-60w Cand.	5" Square	12', 10'
3415 DZ	4-60w Cand.	5" Square	12', 10'
3418 DZ	8-60w Cand.	7" Square	12', 10'

Clarendon is a classic four sided foyer lantern group designed in an elegant two tone finish and constructed in forged iron with cast ball details and clear glass panels. Clarendon is updated tradition at its finest.

FINISH BRONZE
WITH HERITAGE BRASS
GLASS CLEAR

CLARENDON™

Instagram FAVE



@cynthia_weber_design
THE CLARENDON COLLECTION

ADDITIONAL FINISHES
Aged Zinc with Antique Nickel (DZ)



3415 BZ
12" W, 26½" H



3413 BZ
8" W, 18¼" H



3414 BZ
16" W, 33¾" H



3418 BZ
20" W, 44" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3413 BZ	3-60w Cand.	5" Square	12', 10'
3414 BZ	6-60w Cand.	5" Square	12', 10'
3415 BZ	4-60w Cand.	5" Square	12', 10'
3418 BZ	8-60w Cand.	7" Square	12', 10'



The Fleming collection features an updated traditional style with an inventive take on Victorian Age street lighting. The airy simplicity of the open lantern design blends charming details and sweeping lines for an American-chic style that perfectly blends clean and classic.

FINISH POLISHED ANTIQUE NICKEL

FLEMING™




4493 PL
12" W, 24" H



4494 PL
16¾" W, 31" H



4492 PL
8" W, 14¾" H



4497 PL
8" W, 14½" H
47¼" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
4492 PL	2-60w Cand.	4"	9½"	4¾" W, 7½" H Back Plate		
4493 PL	4-60w Cand.			5" Square Canopy	6', 5'	
4494 PL	4-60w Cand.			5" Square Canopy	6', 5'	
4497 PL	1-100w Med.			5" Square Canopy	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PL.


ALISTER™

FINISH ANTIQUE NICKEL


Chic minimalism is captured with Alister's airy, open appearance. The streamlined, stem-hung design exudes sophistication, capturing both clean and classic lines in its timeless silhouette.

ADDITIONAL FINISHES

Buckeye Bronze (KZ)



3078 AN
32" DIA., 29" H
79" MAX. H*




3076 AN
28" DIA., 26" H
76" MAX. H*



3072 AN
10¾" W, 14¼" H



3075 AN
24" DIA., 24" H
74" MAX. H*



3074 AN
33" W, 18½" H
54½" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3072 AN	2-60w Cand.		4"	10"	5" Dia. Back Plate		
3074 AN	8-60w Cand.	14"			4½" W, 8" L Canopy	12'	2-6", 4-12"
3075 AN	6-60w Cand.				6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"
3076 AN	8-60w Cand.				6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"
3078 AN	12-60w Cand.				6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 AN. Ideal for vintage filament bulbs (not included).

ALISTER™


FINISH BUCKEYE BRONZE

Chic minimalism is captured with Alister's airy, open appearance. The streamlined, stem-hung design exudes sophistication, capturing both clean and classic lines in its timeless silhouette.

ADDITIONAL FINISHES
Antique Nickel (AN)



3078 KZ
32" DIA., 29" H
79" MAX. H*



3076 KZ
28" DIA., 26" H
76" MAX. H*



3072 KZ
10¾" W, 14¼" H



3075 KZ
24" DIA., 24" H
74" MAX. H*



3074 KZ
33" W, 18½" H
54½" MAX. H*

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3072 KZ	2-60w Cand.		4"	10"	5" Dia. Back Plate		
3074 KZ	8-60w Cand.	14"			4½" W, 8" L Canopy	12'	2-6", 4-12"
3075 KZ	6-60w Cand.				6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"
3076 KZ	8-60w Cand.				6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"
3078 KZ	12-60w Cand.				6" Dia. Canopy	10'	1-4", 1-6", 1-12", 1-24"

*Maximum achievable height with stems included. Additional 12" stems available, 6036 KZ. Ideal for vintage filament bulbs (not included).

RUTHERFORD™

FINISH
OIL RUBBED BRONZE

Rutherford's traditional simplicity recalls the charm of Williamsburg updated into a lighter, sleeker silhouette. Elegant arms extend confidently from cast spheres while an oversized top loop adds a modern touch. A classic style that complements any décor, Rutherford is an ideal fit for the lower ceiling heights common in traditional homes.



3599 OZ
34" DIA., 17³/₄" H



3595 OZ
24" DIA., 11¾" H



3592 OZ
8¼" W, 11¼" H



3598 OZ
29" DIA., 12½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
3592 OZ	2-60w Cand.	5¾"	9"	5" W, 8½" H Back Plate	
3595 OZ	5-60w Cand.			5" Dia. Canopy	6', 5'
3598 OZ	8-60w Cand.			5" Dia. Canopy	6', 5'
3599 OZ	9-60w Cand.			5" Dia. Canopy	12', 10'

ELEANOR™

FINISH POLISHED ANTIQUE NICKEL

The Eleanor collection offers a classic traditional chandelier arrangement with graceful arms, elegant turnings and sleek candle sleeves. A glamorous center column constructed of solid crystal elements conveys modern sophistication.

ADDITIONAL FINISHES

Heritage Brass (HB), Light Oiled Bronze (LZ)



4959 PL
44¼" DIA., 31¾" H

50



4958 PL
35¼" DIA., 31¼" H



4952 PL
12¾" W, 9" H



4956 PL
27¼" DIA., 22¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4952 PL	2-60w Cand.	6¼"	4½"	4½" W, 7" H Back Plate	
4956 PL	6-60w Cand.			5¼" Dia. Canopy	6', 5'
4958 PL	9-60w Cand.			5¼" Dia. Canopy	12', 10'
4959 PL	15-60w Cand.			5¼" Dia. Canopy	12', 10'

ELEANOR™

FINISH HERITAGE BRASS

The Eleanor collection offers a classic traditional chandelier arrangement with graceful arms, elegant turnings and sleek candle sleeves. A glamorous center column constructed of solid crystal elements conveys modern sophistication.

ADDITIONAL FINISHES

Light Oiled Bronze (LZ), Polished Antique Nickel (PL)



4959 HB
44¼" DIA., 31¾" H





4958 HB
35¼" DIA., 31¼" H

50



4952 HB
12¾" W, 9" H



4956 HB
27¼" DIA., 22¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4952 HB	2-60w Cand.	6¼"	4½"	4½" W, 7" H Back Plate	
4956 HB	6-60w Cand.			5¼" Dia. Canopy	6', 5'
4958 HB	9-60w Cand.			5¼" Dia. Canopy	12', 10'
4959 HB	15-60w Cand.			5¼" Dia. Canopy	12', 10'

ELEANOR™

FINISH LIGHT OILED BRONZE

The Eleanor collection offers a classic traditional chandelier arrangement with graceful arms, elegant turnings and sleek candle sleeves. A glamorous center column constructed of solid crystal elements conveys modern sophistication.

ADDITIONAL FINISHES

Heritage Brass (HB), Polished Antique Nickel (PL)



4959 LZ
44¼" DIA., 31¾" H

50



4958 LZ
35¼" DIA., 31¼" H



4952 LZ
12¾" W, 9" H



4956 LZ
27¼" DIA., 22¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4952 LZ	2-60w Cand.	6¼"	4½"	4½" W, 7" H Back Plate	
4956 LZ	6-60w Cand.			5¼" Dia. Canopy	6', 5'
4958 LZ	9-60w Cand.			5¼" Dia. Canopy	12', 10'
4959 LZ	15-60w Cand.			5¼" Dia. Canopy	12', 10'

WEXLEY™

FINISH HERITAGE BRASS,
OIL RUBBED BRONZE,
POLISHED NICKEL
GLASS CLEAR

Wexley is a distinctive transitional pendant with bold, oval shaped clear glass as the centerpiece of the design. Decorative cast details and crystal accents, combined with rich finish options, make a modern statement with vintage flair.



4325 HB
18" DIA., 27½" H



4325 OZ
18" DIA., 27½" H



4325 PN
18" DIA., 27½" H



4323 HB
12" DIA., 19½" H



4323 OZ
12" DIA., 19½" H



4323 PN
12" DIA., 19½" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
4323 HB, OZ, PN	3-60w Cand.	6" Dia.	6', 5'
4325 HB, OZ, PN	5-60w Cand.	6" Dia.	12', 10'

Ideal for vintage filament bulbs (not included).

ELAINE™

FINISH LIGHT OILED BRONZE

Elaine's updated traditional style resonates with modern appeal. A traditional foyer form with flair, Elaine's clean lines are complemented with elegant sweeping arms, chandelier interior lamping and a stunning solid crystal ball accent.

ADDITIONAL FINISHES

Polished Antique Nickel (PL)



4353 LZ
9 3/4" DIA., 17" H
(mounted as semi-flush)



4353 LZ
9 3/4" DIA., 18 3/4" H



4358 LZ
19" DIA., 43" H



4354 LZ
14" DIA., 27" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
4353 LZ	3-60w Cand.	5 1/4" Dia.	6', 5'
4354 LZ	4-60w Cand.	5 1/4" Dia.	12', 10'
4358 LZ	8-60w Cand.	5 1/4" Dia.	12', 10'

Elaine's updated traditional style resonates with modern appeal. A traditional foyer form with flair, Elaine's clean lines are complemented with elegant sweeping arms, chandelier interior lighting and a stunning solid crystal ball accent.

FINISH POLISHED ANTIQUE NICKEL

ELAINE™

ADDITIONAL FINISHES
Light Oiled Bronze (LZ)



4354 PL
14" DIA., 27" H



4358 PL
19" DIA., 43" H



4353 PL
9¾" DIA., 17" H
(mounted as semi-flush)



4353 PL
9¾" DIA., 18¾" H



ITEM	BULBS	CANOPY	WIRE/CHAIN
4353 PL	3-60w Cand.	5¼" Dia.	6', 5'
4354 PL	4-60w Cand.	5¼" Dia.	12', 10'
4358 PL	8-60w Cand.	5¼" Dia.	12', 10'

GENTRY™

FINISH POLISHED NICKEL
GLASS CLEAR ROUNDED PANELS

Gentry's traditional design is offered in four classic finishes, Heirloom Brass, Olde Bronze, Pewter and Polished Nickel. The clear bent glass panels, white candle sleeves and coordinating candle chasers add classic elegance to this timeless style.

ADDITIONAL FINISHES

Heirloom Brass (HR), Olde Bronze (OB), Pewter (PW)



3479 PN
17" DIA., 40¼" H



3472 PN
9½" DIA., 9¼" H



3473 PN
11½" DIA., 9½" H



3470 PN
8" DIA., 13" H



3478 PN
14" DIA., 25" H



3474 PN
12" DIA., 19¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3470 PN	3-60w Cand.	5½" Dia.	6', 5'
3472 PN	2-40w Cand.	9½" Dia.	
3473 PN	3-40w Cand.	11½" Dia.	
3474 PN	4-60w Cand.	5½" Dia.	6', 5'
3478 PN	6-60w Cand.	5½" Dia.	12', 10'
3479 PN	12-60w Cand.	5½" Dia.	12', 10'

GENTRY™

FINISH PEWTER
GLASS CLEAR ROUNDED PANELS

Gentry's traditional design is offered in four classic finishes, Heirloom Brass, Olde Bronze, Pewter and Polished Nickel. The clear bent glass panels, white candle sleeves and coordinating candle chasers add classic elegance to this timeless style.

ADDITIONAL FINISHES

Heirloom Brass (HR), Olde Bronze (OB), Polished Nickel (PN)



3479 PW
17" DIA., 40¼" H



3472 PW
9½" DIA., 9¼" H



3473 PW
11½" DIA., 9½" H



3470 PW
8" DIA., 13" H



3478 PW
14" DIA., 25" H



3474 PW
12" DIA., 19¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3470 PW	3-60w Cand.	5½" Dia.	6', 5'
3472 PW	2-40w Cand.	9½" Dia.	
3473 PW	3-40w Cand.	11½" Dia.	
3474 PW	4-60w Cand.	5½" Dia.	6', 5'
3478 PW	6-60w Cand.	5½" Dia.	12', 10'
3479 PW	12-60w Cand.	5½" Dia.	12', 10'

GENTRY™

FINISH HEIRLOOM BRASS
GLASS CLEAR ROUNDED PANELS

Gentry's traditional design is offered in four classic finishes, Heirloom Brass, Olde Bronze, Pewter and Polished Nickel. The clear bent glass panels, white candle sleeves and coordinating candle chasers add classic elegance to this timeless style.

ADDITIONAL FINISHES

Olde Bronze (OB), Pewter (PW), Polished Nickel (PN)



3479 HR
17" DIA., 40¼" H



3472 HR
9½" DIA., 9¼" H



3473 HR
11½" DIA., 9½" H



3470 HR
8" DIA., 13" H



3478 HR
14" DIA., 25" H



3474 HR
12" DIA., 19¼" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3470 HR	3-60w Cand.	5½" Dia.	6', 5'
3472 HR	2-40w Cand.	9½" Dia.	
3473 HR	3-40w Cand.	11½" Dia.	
3474 HR	4-60w Cand.	5½" Dia.	6', 5'
3478 HR	6-60w Cand.	5½" Dia.	12', 10'
3479 HR	12-60w Cand.	5½" Dia.	12', 10'

GENTRY™

FINISH OLDE BRONZE
GLASS CLEAR SEEDY
ROUNDED PANELS

Gentry's traditional design is offered in four classic finishes, Heirloom Brass, Olde Bronze, Pewter and Polished Nickel. The clear seedy glass panels, white candle sleeves and coordinating candle chasers add classic elegance to this timeless style.

ADDITIONAL FINISHES

Heirloom Brass (HR), Pewter (PW), Polished Nickel (PN)



3479 OB*
17" DIA., 40¼" H



3472 OB
9½" DIA., 9¼" H



3473 OB
11½" DIA., 9½" H



3470 OB
8" DIA., 13" H



3478 OB*
14" DIA., 25" H



3474 OB*
12" DIA., 19¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
3470 OB	3-60w Cand.	5½" Dia.	6', 5'
3472 OB	2-40w Cand.	9½" Dia.	
3473 OB	3-40w Cand.	11½" Dia.	
3474 OB*	4-60w Cand.	5½" Dia.	6', 5'
3478 OB*	6-60w Cand.	5½" Dia.	12', 10'
3479 OB*	12-60w Cand.	5½" Dia.	12', 10'

*Provided with Olde Bronze and White candle sleeves.

CORDILLERA™

FINISH RUSTIC IRON
GLASS LIGHT SCAVO

Cordillera conveys contemporary chic with tall tubular glass, three-quarter trim rings and dramatic scaling. The Rustic Iron finish is paired with light scavo glass to complete this bold design.



4099 RI
25½" DIA., 46" H



4090 RI
7½" W, 22" H



4094 RI
19" DIA., 36" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
4090 RI	1-60w Cand.	6½"	13"	5¾" W, 10" H Back Plate	
4094 RI	8-40w Cand.			7¼" Dia. Canopy	12', 10'
4099 RI	10-60w Cand.			7¼" Dia. Canopy	12', 10'

Sorrento's flourishing cast metal details are enhanced by hand-applied Aged Iron finish with copper highlights.

FINISH AGED IRON

SORRENTO™



4522 AI
12¼" W, 24" H



4528 AI
16" W, 31¾" H



4526 AI
16¼" W, 23¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
4522 AI	3-60w Cand.	5½" Dia.	12', 10'
4526 AI	4-60w Cand.	5½" Dia.	6', 5'
4528 AI	4-60w Cand.	5½" Dia.	12', 10'

CASA™

FINISH OLDE BLACK
GLASS CLEAR SEEDY

Casa makes the most of its fine details: clear seedy glass, twisted wrought iron and hand-forged scrollwork in an Olde Black finish complete its rustic-chic appeal with a Southwestern flair.

Casa Bath, pages 422-423

ADDITIONAL FINISHES
Olde Black (OL)



4019 OL-CL
42" DIA., 46¼" H





4300 OL-CL
5" W, 23" H



4013 OL-CL
16¾" DIA., 18½" H



4010 OL-CL
5" W, 11¼" H



4015 OL-CL
25" DIA., 25½" H



4018 OL-CL
29" DIA., 31¾" H



4017 OL-CL
5¼" DIA., 12" H
45" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
4010 OL-CL	1-100w Med.	6"	7¼"	5¼" W, 7¾" H Back Plate		
4013 OL-CL	3-100w Med.			5" Dia. Canopy	6', 5'	
4015 OL-CL	5-100w Med.			5" Dia. Canopy	6', 5'	
4017 OL-CL	1-100w Med.			5" Dia. Canopy	10' Wire	1-6", 2-12"
4018 OL-CL	9-100w Med.			5" Dia. Canopy	12', 10'	
4019 OL-CL	15-60w Med.			6" Dia. Canopy	12', 10'	
4300 OL-CL	1-100w Med.	4¼"	10"	5¼" W, 7¾" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 4312 OL.

CASA™

FINISH OLDE BLACK
GLASS ANTIQUE SCAVO

Casa makes the most of its fine details: individually unique antique scavo glass, twisted wrought iron and hand-forged scrollwork in an Olde Black finish complete its rustic-chic appeal with a Southwestern flair.

Casa Bath, pages 422-423

ADDITIONAL FINISHES

Olde Black with Clear Seedy Glass (OL-CL)



4309 OL
56" DIA., 68" H





4013 OL
16¾" DIA., 18½" H



4019 OL
42" DIA., 45½" H



3503 OL
12½" DIA., 17½" H



4015 OL
25" DIA., 25½" H



4018 OL
29" DIA., 31¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN
3503 OL	3-60w Cand.	5" Dia.	12', 10'
4013 OL	3-100w Med.	5" Dia.	6', 5'
4015 OL	5-100w Med.	5" Dia.	6', 5'
4018 OL	9-100w Med.	5" Dia.	12', 10'
4019 OL	15-60w Med.	6" Dia.	12', 10'
4309 OL	18-60w Med.	6½" Dia.	12', 10'



4016 OL
38" W, 24½" H



4308 OL
36½" DIA., 30" H



3504 OL
17¾" DIA., 29¼" H



3506 OL
22½" DIA., 41" H



3502 OL
14¼" DIA., 21" H

ITEM	MAXIMUM WATTAGE	DEPTH	CANOPY	WIRE/CHAIN
3502 OL	3-60w Cand.		5" Dia.	6', 5'
3504 OL	3-100w Med.		5" Dia.	6', 5'
3506 OL	6-100w Med.		5" Dia.	12', 10'
4016 OL	8-75w Med.	24"	5" W, 7" L	6', 5'
4308 OL	8-100w Med.		6½" Dia.	12', 10'



3508 OL
36" DIA., 24½" H



4010 OL
5" W, 10¾" H



4314 OL
27½" DIA., 32" H



4017 OL
5¼" DIA., 13" H
45" MAX. H*



4304 OL
54" W, 28½" H



4300 OL
5" W, 24" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	STEMS INCLUDED
3508 OL	6-100w Med.	23"			5" W, 7" L Canopy	6', 5'	
4010 OL	1-100w Med.		6"	6¾"	5" W, 7¾" H Back Plate		
4017 OL	1-100w Med.				5" Dia. Canopy	10' Wire	1-6", 2-12"
4300 OL	1-100w Med.		4¼"	11¼"	5" W, 7¾" H Back Plate		
4304 OL	6-100w Med.	4"			5" W, 7" L Canopy	6', 5'	
4314 OL	4-75w Med.				6½" Dia. Canopy	6', 5'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 OL.

SUSSEX™

FINISH BRUSHED NICKEL
SHADE WHITE FABRIC HARBACK

Sussex offers traditional charm with an edge of modern luxury. The Brushed Nickel finish, white fabric harback shade, clear glass columns and candles adds to its sophistication.

ADDITIONAL FINISHES
English Bronze (EZ)



4799 BN
47" DIA., 44¼" H

50



4792 BN
15½" W, 15¾" H



4900 BN
14" W, 14" H



4790 BN
4¾" W, 18" H



4796 BN
36¾" W, 23¾" H



4798 BN
32" DIA., 34½" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4790 BN	1-60w Cand.		7"	11"	4¾" W, 14" H Back Plate	
4792 BN	2-60w Cand.		6¾"	8½"	4¾" W, 14" H Back Plate	
4796 BN	6-60w Cand.	22"			4¾" W, 14" L Canopy	6', 5'
4798 BN	9-60w Cand.				6¾" Dia. Canopy	12', 10'
4799 BN	15-40w Cand.				6¾" Dia. Canopy	12', 10'
4900 BN	2-60w Cand.		4"	7"	4¾" W, 14" H Back Plate	



4793 BN
16" DIA., 19¼" H



4797 BN
23" DIA., 24" H



4791 BN
16" DIA., 15" H



4795 BN
26" DIA., 24¾" H



4794 BN
22" DIA., 26¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
4791 BN	3-75w Med.	6¾" Dia.	
4793 BN	3-60w Cand.	6¾" Dia.	6', 5"
4794 BN	3-75w Med.	6¾" Dia.	12', 10"
4795 BN	5-60w Cand.	6¾" Dia.	6', 5"
4797 BN	4-60w Cand.	6¾" Dia.	12', 10"

Sussex offers traditional charm with an edge of modern luxury. The English Bronze finish, ivory fabric hardback shade, clear glass columns and candles adds to its sophistication.

FINISH ENGLISH BRONZE
SHADE IVORY FABRIC HARDBACK

SUSSEX™

ADDITIONAL FINISHES
Brushed Nickel (BN)



4799 EZ
47" DIA., 44¼" H





4792 EZ
15½" W, 15¾" H



4900 EZ
14" W, 14" H



4790 EZ
4¾" W, 18" H



4796 EZ
36¾" W, 23¾" H



4798 EZ
32" DIA., 34½" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4790 EZ	1-60w Cand.		7"	11"	4¾" W, 14" H Back Plate	
4792 EZ	2-60w Cand.		6¾"	8½"	4¾" W, 14" H Back Plate	
4796 EZ	6-60w Cand.	22"			4¾" W, 14" L Canopy	6', 5'
4798 EZ	9-60w Cand.				6¾" Dia. Canopy	12', 10'
4799 EZ	15-40w Cand.				6¾" Dia. Canopy	12', 10'
4900 EZ	2-60w Cand.		4"	7"	4¾" W, 14" H Back Plate	



4793 EZ
16" DIA., 19¼" H



4797 EZ
23" DIA., 24" H



4791 EZ
16" DIA., 15" H



4795 EZ
26" DIA., 24¾" H



4794 EZ
22" DIA., 26¾" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/CHAIN
4791 EZ	3-75w Med.	6¾" Dia.	
4793 EZ	3-60w Cand.	6¾" Dia.	6', 5'
4794 EZ	3-75w Med.	6¾" Dia.	12', 10'
4795 EZ	5-60w Cand.	6¾" Dia.	6', 5'
4797 EZ	4-60w Cand.	6¾" Dia.	12', 10'

PLYMOUTH™

FINISH POLISHED ANTIQUE NICKEL
GLASS ETCHED WHITE
SHADE SILVER ORGANZA WITH
DECORATIVE FABRIC TRIM

Classic never goes out of style. Plymouth's sweeping arms and vintage inspired candle sleeves with curved cast detailing are enhanced by the hand-rubbed Polished Antique Nickel finish and silver organza shade.

ADDITIONAL FINISHES
Olde Bronze (OB)



4249 PL
44½" DIA., 45" H

50



4240 PL
6½" W, 14" H



4245 PL
34" W, 22½" H



4246 PL
27¾" DIA., 24¼" H



4243 PL
18¼" DIA., 25¼" H



4248 PL
32¼" DIA. 31" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
4240 PL	1-60w Cand.		7½"	8½"	4½" W, 9¼" H Back Plate	
4243 PL	3-60w Cand.				5½" Dia. Canopy	6', 5'
4245 PL	6-60w Cand.	18½"			4½" W, 8" L Canopy	6', 5'
4246 PL	6-60w Cand.				5½" Dia. Canopy	6', 5'
4248 PL	9-60w Cand.				5½" Dia. Canopy	12', 10'
4249 PL	15-40w Cand.				5½" Dia. Canopy	12', 10'



4259 PL
30" DIA., 55½" H



4247 PL
6½" DIA., 10½" H
43" MAX. H*



4254 PL
17¾" DIA., 33½" H



4258 PL
24" DIA., 43" H

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4247 PL	1-100w Med.	5½" Dia.	10' Wire	1-6", 2-12"
4254 PL	4-60w Cand.	5½" Dia.	12', 10'	
4258 PL	8-60w Cand.	5½" Dia.	12', 10'	
4259 PL	9-60w Cand.	5½" Dia.	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PL.

Classic never goes out of style. Plymouth's sweeping arms and vintage inspired candle sleeves with curved cast detailing are enhanced by the hand-rubbed Olde Bronze finish and light amber organza shade.

FINISH OLDE BRONZE
GLASS MOCHA COLORED
SHADE LIGHT AMBER ORGANZA
WITH DECORATIVE FABRIC TRIM

PLYMOUTH™

ADDITIONAL FINISHES
Polished Antique Nickel (PL)



4249 OB
44½" DIA., 45" H





4245 OB
34" W, 22½" H



4240 OB
6½" W, 14" H



4243 OB
18¼" DIA., 25¼" H



4248 OB
32¼" DIA. 31" H



4246 OB
27¾" DIA., 24¼" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
4240 OB	1-60w Cand.		7½"	8½"	4½" W, 9¼" H Back Plate	
4243 OB	3-60w Cand.				5½" Dia. Canopy	6', 5'
4245 OB	6-60w Cand.	18½"			4½" W, 8" L Canopy	6', 5'
4246 OB	6-60w Cand.				5½" Dia. Canopy	6', 5'
4248 OB	9-60w Cand.				5½" Dia. Canopy	12', 10'
4249 OB	15-40w Cand.				5½" Dia. Canopy	12', 10'



4247 OB
6½" DIA., 10½" H
43" MAX. H*



4258 OB
24" DIA., 43" H



4254 OB
17¾" DIA., 33½" H



4259 OB
30" DIA., 55½" H

50

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4247 OB	1-100w Med.	5½" Dia.	10' Wire	1-6", 2-12"
4254 OB	4-60w Cand.	5½" Dia.	12', 10'	
4258 OB	8-60w Cand.	5½" Dia.	12', 10'	
4259 OB	9-60w Cand.	5½" Dia.	12', 10'	

*Maximum achievable height with stems included. Additional 12" stems available, 4312 OB.

PLANTATION™

FINISH PEARL BRONZE
GLASS CLEAR OPTIC
SHADE IVORY SILK

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped, clear optic glass that makes a noble statement with matching candle sleeves and elaborate, decorative cast detailing.

Plantation Bath, pages 424-425

ADDITIONAL FINISHES

Burnished Brass (BB), Polished Antique Nickel (PL)



4889 PZ
56" DIA., 54" H





4880 PZ
6" W, 15" H



4887 PZ
33" DIA., 36¾" H



5317 PZ
5" DIA. 8¼" H
40¾" MAX. H*



4886 PZ
28" DIA., 33" H



4140 PZ
6" W, 14½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4140 PZ	1-60w Cand.	8½"	8½"	4¾" W, 12" H Back Plate		
4880 PZ	1-60w Cand.	8¾"	10¾"	6" Dia. Back Plate		
4886 PZ	7-60w Cand.**			6" Dia. Canopy	6', 5'	
4887 PZ	10-60w Cand.**			6" Dia. Canopy	12', 10'	
4889 PZ	21-25w Cand., 1-25w Med.**			6" Dia. Canopy	12', 10'	
5317 PZ	1-100w Med.			6" Dia. Canopy	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PZ. **Lighted center font, switched.



4102 PZ
12" DIA., 8" H



4881 PZ
16" DIA., 8¾" H



5310 PZ
5" W, 8¾" H



4103 PZ
13" DIA., 19" H



4885 PZ
22" DIA., 24½" H



2222 PZ
12½" DIA., 28½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2222 PZ	4-40w Cand.			6" Dia. Canopy	6', 5'
4102 PZ	2-60w Med.				
4103 PZ	3-60w Cand.			6" Dia. Canopy	12', 10'
4881 PZ	3-60w Med.				
4885 PZ	5-75w Med.			6" Dia. Canopy	6', 5'
5310 PZ	1-100w Med.	7"	5"	5" W, 8" H Back Plate	

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped, clear optic glass that makes a noble statement with matching candle sleeves and elaborate, decorative cast detailing.

Plantation Bath, pages 424-425

FINISH BURNISHED BRASS
GLASS CLEAR OPTIC
SHADE IVORY SILK

PLANTATION™

ADDITIONAL FINISHES

Pearl Bronze (PZ), Polished Antique Nickel (PL)



4889 BB
56" DIA., 54" H





4880 BB
6" W, 15" H



4887 BB
33" DIA., 36¾" H



5317 BB
5" DIA. 8¼" H
40¾" MAX. H*



4886 BB
28" DIA., 33" H



4140 BB
6" W, 14½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN	STEMS INCLUDED
4140 BB	1-60w Cand.	8½"	8½"	4¾" W, 12" H Back Plate		
4880 BB	1-60w Cand.	8¾"	10¾"	6" Dia. Back Plate		
4886 BB	7-60w Cand.**			6" Dia. Canopy	6', 5'	
4887 BB	10-60w Cand.**			6" Dia. Canopy	12', 10'	
4889 BB	21-25w Cand., 1-25w Med.**			6" Dia. Canopy	12', 10'	
5317 BB	1-100w Med.			6" Dia. Canopy	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PZ. **Lighted center font, switched.



4102 BB
12" DIA., 8" H



4881 BB
16" DIA., 8¾" H



5310 BB
5" W, 8¾" H



4103 BB
13" DIA., 19" H



4885 BB
22" DIA., 24½" H



2222 BB
12½" DIA., 28½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2222 BB	4-40w Cand.			6" Dia. Canopy	6', 5'
4102 BB	2-60w Med.				
4103 BB	3-60w Cand.			6" Dia. Canopy	12', 10'
4881 BB	3-60w Med.				
4885 BB	5-75w Med.			6" Dia. Canopy	6', 5'
5310 BB	1-100w Med.	7"	5"	5" W, 8" H Back Plate	

PLANTATION™

FINISH POLISHED
ANTIQUE NICKEL
GLASS CLEAR OPTIC
SHADE IVORY SILK

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped, clear optic glass that makes a noble statement with matching candle sleeves and elaborate, decorative cast detailing.

Plantation Bath, pages 424-425

ADDITIONAL FINISHES

Burnished Brass (BB), Pearl Bronze (PZ)



4886 PL
28" DIA., 33" H



4881 PL
16" DIA., 8¾" H



4102 PL
12" DIA., 8" H



4880 PL
6" W, 15" H



5317 PL
5" DIA, 8¼" H
40¾" MAX. H*



5310 PL
5" W, 8¾" H



2222 PL
12½" DIA., 28½" H



4103 PL
13" DIA, 19" H



4885 PL
22" DIA, 24½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
2222 PL	4-40w Cand.			6" Dia. Canopy	6', 5'	
4102 PL	2-60w Med.					
4103 PL	3-60w Cand.			6" Dia. Canopy	12', 10'	
4880 PL	1-60w Cand.	8¾"	10¾"	6" Dia. Back Plate		
4881 PL	3-60w Med.					
4885 PL	5-60w Med.			6" Dia. Canopy	6', 5'	
4886 PL	7-60w Cand.**			6" Dia. Canopy	6', 5'	
5310 PL	1-100w Med.	7"	5"	5" W, 8" H Back Plate		
5317 PL	1-100w Med.			6" Dia. Canopy	10' Wire	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PL. **Lighted center font, switched.

CARLTON™

FINISH SILVER LEAF
SHADE ORGANZA (OPTIONAL)

Carlton's elegant petite candelabra iron design, finished in authentic Silver Leaf, makes a sophisticated statement with luxurious amber pearl crystals, optional translucent organza shade and ornate details.



4779 SL
45" DIA., 45½" H

50



4775 SL
24" DIA., 25" H



4771 SL
24" DIA., 17½" H
(shade included)



4774 SL
18" DIA., 22" H



4772 SL
12½" W, 19" H



4776 SL
28" DIA., 28½" H
(shown with optional shade)



4770 SH
4" DIA., 4¾" H
(optional shade)



4778 SL
35" DIA., 36½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
4770 SH	Do not exceed 40w				
4771 SL	4-60w Cand.			6" Dia. Canopy	
4772 SL	2-60w Cand.	7"	9¼"	5" Dia. Back Plate	
4774 SL	4-60w Cand.			6" Dia. Canopy	6', 5'
4775 SL	5-60w Cand.			6" Dia. Canopy	6', 5'
4776 SL	6-60w Cand.			6" Dia. Canopy	6', 5'
4778 SL	12-60w Cand.			6" Dia. Canopy	12', 10'
4779 SL	21-40w Cand.			6" Dia. Canopy	12', 10'

MARCELLINA™

FINISH GOLDEN BRONZE
SHADE DAMASK SILK (OPTIONAL)

Marcellina's grand style features beautiful, silver-highlighted cast leaf detailing, crystal bobeches, crystal ball finials and a large solid crystal center gazing ball. The Golden Bronze finish and optional damask silk shades add to the collection's luxurious sophistication.



4408 GR
47" DIA., 53" H



4405 GR
25" DIA., 28" H



4401 OW
5¾" DIA., 6½" H
(optional shade)



4400 GR
6½" W, 19" H



4404 GR
39" DIA., 42" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
4400 GR	1-60w Cand.	6½"	7"	6½" W, 11½" H Back Plate	
4401 OW	Do not exceed 40w				
4404 GR	8-60w Cand.			6¼" Dia. Canopy	12', 10'
4405 GR	5-60w Cand.			6¼" Dia. Canopy	12', 10'
4408 GR	15-60w Cand.			6¼" Dia. Canopy	12', 10'

CAMBRIDGE™

FINISH BURNISHED BRASS
 GLASS CLEAR OPTIC
 SHADE PLEATED OFF-WHITE FABRIC
 (OPTIONAL); 3610 BB IVORY HARBACK
 LINEN FABRIC SHADE (INCLUDED)

Cambridge offers classic New England appeal. The solid cast components, brass turnings, beaded ball fonts and clear optic glass reinforce its timeless style. Available in Pewter, Burnished Brass and Olde Bronze finishes.

ADDITIONAL FINISHES

Olde Bronze (OB), Pewter (PW)



4412 BB
 13½" W, 10¾" H
 (shown with optional shade)



4410 BB
 4½" W, 10¾" H



4417 BB
 37" DIA., 34¾" H



4419 BB
 49¼" DIA., 46¾" H



4421 OW
 5½" DIA., 5" H
 (optional shade)

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
4410 BB	1-60w Cand.	9¼"	6¼"	4½" W, 6½" H Back Plate	
4412 BB	2-60w Cand.	9¼"	6¼"	4½" W, 6½" H Back Plate	
4417 BB	15-40w Cand.			6¼" Dia. Canopy	12', 10'
4419 BB	25-25w Cand.			7" Dia. Canopy	12', 10'
4421 OW	Do not exceed 40w				



3612 BB
14½" DIA., 13" H



3610 BB
14½" W, 18" H
(shade included)



3616 BB
16¼" DIA., 7½" H



4415 BB
25¼" DIA., 24" H



4416 BB
29" DIA., 26¼" H



3613 BB
21¼" DIA., 21", 22½"* H



4642 BB
14" W, 13½" H



4640 BB
4½" W, 13" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
3610 BB	2-60w Cand.	4"	14"	4¾" W, 7¾" H Back Plate	
3612 BB	3-60w Cand.				
3613 BB	3-60w Cand.			6¾" Dia. Canopy	12', 10'
3616 BB	2-60w Med.				
4415 BB	5-60w Cand.			6¼" Dia. Canopy	6', 5'
4416 BB	6-60w Cand.			6¼" Dia. Canopy	6', 5'
4640 BB	1-60w Cand.	9½"	9½"	4½" W, 6½" H Back Plate	
4642 BB	2-60w Cand.	8"	9"	4½" W, 6½" H Back Plate	

*Height when hung with chain (includes loop).

CAMBRIDGE™

FINISH PEWTER
 GLASS CLEAR OPTIC
 SHADE BLACK PARCHMENT WITH GOLD
 LINING (OPTIONAL); 3610 PW IVORY
 HARDBACK LINEN FABRIC SHADE (INCLUDED)

Cambridge offers classic New England appeal. The solid cast components, brass turnings, beaded ball fonts and clear optic glass reinforce its timeless style. Available in Pewter, Burnished Brass and Olde Bronze finishes.

ADDITIONAL FINISHES

Burnished Brass (BB), Olde Bronze (OB)



3616 PW
 16¼" DIA., 7½" H



3613 PW
 21¼" DIA., 21", 22½"* H



3612 PW
 14½" DIA., 13" H



4412 PW
 13½" W, 10¾" H
 (shown with optional shade)



3610 PW
 14½" W, 18" H
 (shade included)



4410 PW
 4½" W, 10¾" H



5122 BK
 5½" DIA., 5" H
 (optional shade)

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
3610 PW	2-60w Cand.	4"	14"	4¾" W, 7¾" H Back Plate	
3612 PW	3-60w Cand.				
3613 PW	3-60w Cand.			6¾" Dia. Canopy	12', 10'
3616 PW	2-60w Med.				
4410 PW	1-60w Cand.	9¼"	6¼"	4½" W, 6½" H Back Plate	
4412 PW	2-60w Cand.	9¼"	6¼"	4½" W, 6½" H Back Plate	
5122 BK	Do not exceed 40w				

*Height when hung with chain (includes loop).

Cambridge offers classic New England appeal. The solid cast components, brass turnings, beaded ball fonts and clear optic glass reinforce its timeless style. Available in Pewter, Burnished Brass and Olde Bronze finishes.

FINISH OLDE BRONZE
GLASS CLEAR OPTIC
SHADE PLEATED OFF-WHITE FABRIC
(OPTIONAL); 3610 OB IVORY HARDBACK
LINEN FABRIC SHADE (INCLUDED)

CAMBRIDGE™

ADDITIONAL FINISHES
Burnished Brass (BB), Pewter (PW)



3612 OB
14½" DIA., 13" H



3613 OB
21¼" DIA., 21", 22½"* H



3616 OB
16¼" DIA., 7½" H



3610 OB
14½" W, 18" H
(shade included)



4412 OB
13½" W, 10¾" H
(shown with optional shade)



4421 OW
5½" DIA., 5" H
(optional shade)



4410 OB
4½" W, 10¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
3610 OB	2-60w Cand.	4"	14"	4¾" W, 7¾" H Back Plate	
3612 OB	3-60w Cand.				
3613 OB	3-60w Cand.			6¾" Dia. Canopy	12', 10'
3616 OB	2-60w Med.				
4410 OB	1-60w Cand.	9¼"	6¼"	4½" W, 6½" H Back Plate	
4412 OB	2-60w Cand.	9¼"	6¼"	4½" W, 6½" H Back Plate	
4421 OW	Do not exceed 40w				

*Height when hung with chain (includes loop).

ROCKFORD™

FINISH FORUM BRONZE
GLASS CLEAR SEEDY HURRICANE

Rockford's bold traditional design features a cast urn centerpiece, candle chasers and beaded cast metal bobeches in a classic Forum Bronze finish. The clear seedy hurricane glass adds to its authentic appeal.



4626 FB
26¾" DIA., 29¼" H



3716 FB
16¼" DIA., 7½" H



3712 FB
14½" DIA., 12½" H



4622 FB
14" W, 13½" H



4620 FB
5" W, 13" H



3713 FB
20¾" DIA., 20¾", 24¼" H



3714 FB
23" DIA., 42½" H


ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
3712 FB	3-40w Cand.				
3713 FB	3-60w Cand.			6¾" Dia. Canopy	6', 10'
3714 FB	3-60w Cand.			6¾" Dia. Canopy	12', 10'
3716 FB	2-60w Med.				
4620 FB	1-60w Cand.	9½"	8½"	4½" W, 6½" H Back Plate	
4622 FB	2-60w Cand.	7½"	9"	4½" W, 6½" H Back Plate	
4626 FB	6-60w Cand.			6¾" Dia. Canopy	6', 5'

*Height when hung with chain (includes loop).



"I've been drawn to antique brass lately due to its characteristic warmth and allure, but I generally mix finishes, rarely sticking to one palette. What I find most important in a chandelier is that it has clean, controlled lines and a masterfully applied finish."

ABOVE: THE QUENTIN + MERCER COLLECTIONS | 4815KZ, PAGE 128 AND 3650HB, PAGE 303



MARIE FLANIGAN
MARIE FLANIGAN INTERIORS
HOUSTON, TX

Synonymous with vintage glamour, Mercer's mid-century modern design has a cool simplicity that blends robust metal construction and circular glass shades that emit a soft glow, creating a perfect accent for any decor.

FINISH ANTIQUE NICKEL,
HERITAGE BRASS,
OIL RUBBED BRONZE,
POLISHED NICKEL
GLASS ETCHED OPAL

MERCER™

INSTAFAVE



@ramagecompany
THE MERCER COLLECTION



3650 AN
6¾" W, 6¾" H



3650 HB
6¾" W, 6¾" H



3650 OZ
6¾" W, 6¾" H



3650 PN
6¾" W, 6¾" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3650 AN	1-60w Cand.	4"	3½"	6" Dia.
3650 HB	1-60w Cand.	4"	3½"	6" Dia.
3650 OZ	1-60w Cand.	4"	3½"	6" Dia.
3650 PN	1-60w Cand.	4"	3½"	6" Dia.


LANZA™

FINISH ANTIQUE NICKEL, BRUSHED BRONZE, OIL RUBBED BRONZE
SHADE OFF-WHITE LINEN
HARDBACK, OATMEAL LINEN


Lanza makes a chic statement with its strong, rectangular metal work. The geometric detailing is softened with linen shades for a warm sophisticated look.




3162 AN
 10" W, 11½" H




3162 BR
 10" W, 11½" H




3162 OZ
 10" W, 11½" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3162 AN	2-60w Cand.	4"	3½"	5½" W, 5¾" H
3162 BR	2-60w Cand.	4"	3½"	5½" W, 5¾" H
3162 OZ	2-60w Cand.	4"	3½"	5½" W, 5¾" H

Avenue offers three distinct silhouettes in Brushed Nickel and Oil Rubbed Bronze to fit any style of décor. The patented LED technology produces as much light as a 100w bulb while consuming only 1/6 the energy. This LED sconce is fully dimmable and ADA compliant.

FINISH BRUSHED NICKEL,
OIL RUBBED BRONZE
SHADE LINEN

AVENUE™



61111 BN
5" W, 12¾" H
T24 ADA



61111 OZ
5" W, 12¾" H
T24 ADA



61033 BN
5" W, 7¾" H
T24 ADA



61033 OZ
5" W, 7¾" H
T24 ADA



61222 BN
5" W, 8" H
T24 ADA



61222 OZ
5" W, 8" H
T24 ADA

LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
61033 BN	16w LED	930	2700	91	1-100w	3¾"	4"	5" W, 7¾" H
61033 OZ	16w LED	930	2700	91	1-100w	3¾"	4"	5" W, 7¾" H
61111 BN	16w LED	930	2700	91	1-100w	4"	5"	5" W, 7¾" H
61111 OZ	16w LED	930	2700	91	1-100w	4"	5"	5" W, 7¾" H
61222 BN	16w LED	930	2700	91	1-100w	4"	4"	5" W, 7¾" H
61222 OZ	16w LED	930	2700	91	1-100w	4"	4"	5" W, 7¾" H

For complete product details and LED specifications, refer to hinkleylighting.com.

HADLEY™

FINISH ANTIQUE NICKEL,
BRUSHED BRONZE, CHROME,
OIL RUBBED BRONZE
GLASS CLEAR, ETCHED OPAL

Hadley is a retro-styled collection available in four classic finish options: Antique Nickel, Brushed Bronze, Chrome and Oil Rubbed Bronze. The clear or etched opal, one piece glass shade features a slim design that will complement a variety of decors.



3302 AN
3302 AN-LED
12" DIA., 4¾" H



3302 AN-CL
12" DIA., 4¾" H



3302 OZ
3302 OZ-LED
12" DIA., 4¾" H



3302 OZ-CL
12" DIA., 4¾" H



3302 BR
3302 BR-LED
12" DIA., 4¾" H



3302 BR-CL
12" DIA., 4¾" H



3302 CM
3302 CM-LED
12" DIA., 4¾" H



3302 CM-CL
12" DIA., 4¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.
3302 AN, BR, CM, OZ	2-60w Med.	3302 AN-LED, BR-LED, CM-LED, OZ-LED	16w LED	950	2700	96	1-100w
3302 AN-CL, BR-CL, CM-CL, OZ-CL	2-60w Med.						


For complete product details and LED specifications, refer to hinkleylighting.com.

Hadley is a retro-styled collection available in four classic finish options: Antique Nickel, Brushed Bronze, Chrome and Oil Rubbed Bronze. The etched opal, one piece glass shade features a slim design that will complement a variety of decors.


FINISH ANTIQUE NICKEL,
BRUSHED BRONZE, CHROME,
OIL RUBBED BRONZE
GLASS ETCHED OPAL

HADLEY™



3304 AN
3304 AN-LED
20" DIA., 7¾" H




3304 BR
3304 BR-LED
20" DIA., 7¾" H




3304 OZ
3304 OZ-LED
20" DIA., 7¾" H




3304 CM
3304 CM-LED
20" DIA., 7¾" H


ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.
3304 AN	4-60w Med.	3304 AN-LED	48w LED	2850	2700	96	3-100w
3304 BR	4-60w Med.	3304 BR-LED	48w LED	2850	2700	96	3-100w
3304 CM	4-60w Med.	3304 CM-LED	48w LED	2850	2700	96	3-100w
3304 OZ	4-60w Med.	3304 OZ-LED	48w LED	2850	2700	96	3-100w



For complete product details and LED specifications, refer to hinkleylighting.com.

HADLEY™



FINISH ANTIQUE NICKEL,
BRUSHED BRONZE, CHROME,
OIL RUBBED BRONZE
GLASS CLEAR, ETCHED OPAL

Hadley is a retro-styled collection available in four classic finish options: Antique Nickel, Brushed Bronze, Chrome and Oil Rubbed Bronze. The clear or etched opal, one piece glass shade features a slim design that will complement a variety of decors.





3300 AN
3300 AN-LED
7¾" DIA., 7" H
 





3300 OZ
3300 OZ-LED
7¾" DIA., 7" H
 



3300 BR
3300 BR-LED
7¾" DIA., 7" H
 



3300 CM
3300 CM-LED
7¾" DIA., 7" H
 



3300 AN-CL
7¾" DIA., 7" H



3300 OZ-CL
7¾" DIA., 7" H



3300 BR-CL
7¾" DIA., 7" H



3300 CM-CL
7¾" DIA., 7" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.
3300 AN, BR, CM, OZ	1-100w Med.	3300 AN-LED, BR-LED, CM-LED, OZ-LED	15w LED	900	2700	96	1-75w
3300 AN-CL, BR-CL, CM-CL, OZ-CL	1-100w Med.						

For complete product details and LED specifications, refer to hinkleylighting.com.

The Hadley is a retro-styled collection available in four classic finish options: Antique Nickel, Brushed Bronze, Chrome and Oil Rubbed Bronze. The etched opal, one piece glass shade features a slim design that will complement a variety of decors.

FINISH ANTIQUE NICKEL,
BRUSHED BRONZE, CHROME,
OIL RUBBED BRONZE
GLASS ETCHED OPAL

HADLEY™



3308 AN
3308 AN-QF*
7¾" DIA., 4½" H



3308 OZ
3308 OZ-QF*
7¾" DIA., 4½" H



3308 BR
3308 BR-QF*
7¾" DIA., 4½" H



3308 CM
3308 CM-QF*
7¾" DIA., 4½" H



3301 AN
3301 AN-LED
14" DIA., 5½" H



3301 BR
3301 BR-LED
14" DIA., 5½" H



3308 OZ
(shown mounted as a sconce)



3301 OZ
3301 OZ-LED
14" DIA., 5½" H



3301 CM
3301 CM-LED
14" DIA., 5½" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.
3301 AN, BR, CM, OZ	3-60w Med.	3301 AN-LED, BR-LED, CM-LED, OZ-LED	32w LED	1900	2700	96	2-100w
		3308 AN, BR, CM, OZ	16w LED	930	2700	96	1-100w
		3308 AN-QF*, BR-QF*, CM-QF*, OZ-QF*	16w LED	930	2700	96	1-100w

*3308 XX-QF includes QuickFit recessed light converter kit, 80100 QF, also available separately. See page 185. For complete product details and LED specifications, refer to hinkleylighting.com

MAXWELL™

FINISH ANTIQUE NICKEL,
HERITAGE BRASS, OIL RUBBED BRONZE
GLASS ETCHED OPAL

Maxwell combines style elements that span across retro modern and traditional style lines for wide appeal. The sleek etched opal glass shade and prominent knobs add vintage flair.



3783 AN
3783 AN-LED
19" DIA., 6½" H



3783 OZ
3783 OZ-LED
19" DIA., 6½" H



3783 HB
3783 HB-LED
19" DIA., 6½" H



3782 AN
13¾" DIA., 5" H



3782 OZ
13¾" DIA., 5" H



3782 HB
13¾" DIA., 5" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.
3782 AN, HB, OZ	2-40w Med.						
3783 AN, HB, OZ	3-60w Med.	3783 AN-LED, HB-LED, OZ-LED	30w LED	2300	2700K	96	2-100w

For complete product details and LED specifications, refer to hinkleylighting.com.

Colbin is sleek, chic and poised. Its etched opal glass and decorative knurled knobs enhance a design that easily crosses style boundaries, from traditional to modern.

FINISH AGED ZINC, BRUSHED
NICKEL, OIL RUBBED BRONZE
GLASS ETCHED OPAL

COLBIN™



3233 BN
16½" DIA., 5¾" H



3233 OZ
16½" DIA., 5¾" H



3233 DZ
16½" DIA., 5¾" H



3231 BN
12½" DIA., 4¾" H



3231 OZ
12½" DIA., 4¾" H



3231 DZ
12½" DIA., 4¾" H

ITEM	MAXIMUM WATTAGE	CANOPY
3231 BN, DZ, OZ	2-60w Med.	11" Dia.
3233 BN, DZ, OZ	3-60w Med.	14¾" Dia.

WESTON™

FINISH BRUSHED NICKEL,
BUCKEYE BRONZE
GLASS ETCHED OPAL

Weston's transitional flush mount style features a blown etched opal glass shade supported by a center ring and three crisp angled arms fastened by decorative knobs. This simple and elegant collection embodies the essence of transitional design, making it the perfect choice for almost any space.



3972 BN
15" DIA., 5¾" H



3972 KZ
15" DIA., 5¾" H



3971 BN
13½" DIA., 5" H



3971 KZ
13½" DIA., 5" H

ITEM	MAXIMUM WATTAGE
3971 BN, KZ	2-60w Med.
3972 BN, KZ	3-60w Med.

Halsey's eye-catching slim profile design is created by the sleek blown etched opal glass shade with vertical sidewalls transitioning to a slightly domed bottom. The intersecting square tube frame follows the contour of the glass shade and invisibly attaches to the canopy, further enhancing this clean and sleek design.

FINISH BRUSHED NICKEL,
BUCKEYE BRONZE
GLASS ETCHED OPAL

HALSEY™



4382 BN
17" DIA., 5¼" H



4382 KZ
17" DIA., 5¼" H



4381 BN
13" DIA., 4½" H



4381 KZ
13" DIA., 4½" H

ITEM	MAXIMUM WATTAGE
4381 BN, KZ	2-60w Med.
4382 BN, KZ	3-60w Med.

HARPER™

FINISH BRUSHED NICKEL,
CHROME, HERITAGE BRASS,
OIL RUBBED BRONZE
GLASS ETCHED OPAL

Harper's sleek, retro design elevates the traditional flush mount with a unique opal glass bound by a prominent metal ring and decorative knobs available in four finishes.



3643 BN
18" DIA., 10" H



3643 HB
18" DIA., 10" H



3643 OZ
18" DIA., 10" H



3643 CM
18" DIA., 10" H



3641 BN
14½" DIA., 10" H



3641 HB
14½" DIA., 10" H



3641 OZ
14½" DIA., 10" H



3641 CM
14½" DIA., 10" H

ITEM	MAXIMUM WATTAGE	CANOPY
3641 BN, CM, HB, OZ	3-100w Med.	7" Dia.
3643 BN, CM, HB, OZ	3-100w Med.	7" Dia.



BECKI OWENS
BECKIOWENS.COM
SOUTHERN CALIFORNIA

"In large master bathrooms I like to emphasize the natural light with crystal, glass or metal light fixtures that feel fresh and airy."

ABOVE: THE LATITUDE COLLECTION | 5651OZ, PAGE 341
OPPOSITE PAGE: THE BOYER COLLECTION | 5262PN, PAGE 369

BATH COLLECTIONS



ABBIE	405	BRANTLEY	414	FAYE	383	MILEY	354	TESSA	353
ACCLAIM	322	BROOKE	416	FRANCOISE	420	PINNACLE	362	THISTLEDOWN	400
AINSLEY	380	CASA	422	JACKSON	370	PLANTATION	424	TREMONT	325
ALICE	392	CHLOE	338	JOSIE	385	PORTIA	323	UNITY	324
ASHLEY	384	CLANCY	373	KARLIE	358	REESE	419	VERVE	342
AVON	349	COLETTE	402	KYRA	356	RIGBY	378	WINTON	328
BALDWIN	394	CONGRESS	374	LANZA	343	SADIE	396	YORKTOWN	408
BENNETT	366	DAPHNE	335	LATITUDE	339	SAN SIMEON	426		
BLYTHE	412	DARBY	397	LAUREL	360	SHELLY	410		
BOLLA	386	DARIA	332	MERIDIAN	364	SIMI	320		
BOYER	368	FAIRLANE	326	MILA	330	TAYLOR	346		

SPA- LIKE

S E R E N I T Y

"From tranquil relaxation to rapid preparation, bathrooms are function-driven spaces. Dim, peaceful lighting helps set the mood for a soak, but we also need brighter, more lively sources of light to apply makeup and select clothing. Tackling all of these tasks successfully relies on an appropriate lighting plan."



MARIE FLANIGAN

MARIE FLANIGAN INTERIORS | HOUSTON, TX





THE OPTICS OF ILLUMINATION

FOUR KEY AREAS OF LIGHT SOURCES ARE RECOMMENDED TO ENSURE YOUR BATHROOM IS AWASH IN ILLUMINATION. USE THIS CHECK LIST TO ENSURE YOUR BATH LIGHTING MAKES A CLEAN SWEEP.

1 CHALLENGE
Exceptional light for daily grooming
Type: Task



SOLUTION Sconces or linear bath bars

2 CHALLENGE
Additional glow from the ceiling with added visual interest
Type: Ambient




SOLUTION Flush or semi-flush mounts, chandeliers

3 CHALLENGE
Highlight special architectural details to create a spa-like setting
Type: Accent



SOLUTION Sconces or flush mounts

4 CHALLENGE
Express personal style
Type: Decorative



SOLUTION Chandeliers, pendants and sconces

ABOVE: 1. SHELLY 5010CM, PAGE 411 | 2. HAMPTON 3211AN, PAGE 169 | 3. BOLLA 4650BN, PAGE 386 | 4. NANTUCKET 2372AS, PAGE 588

a new play on

PENDANTS



ABOVE: THE LANZA + HAMPTON COLLECTIONS
5100AN, PAGE 343 AND 3207AN, PAGE 170

Want a change of scenery in your bath?

PONDER ON PENDANTS.

This versatile type of lighting is more popular than ever and is finding itself at home in all kinds of unexpected environments. Pendants lend an amplified feeling of indulgence to an area that is already concentrated on inspiring feelings of relaxation, rejuvenation and respite from the daily hustle. With their slim profile, pendants are perfect for smaller spaces, boosting ambient light and injecting a serious dose of style. Controlling the level of light you want from your pendants with a dimmer gives you additional control over how the space functions: brighten up with extra light during the kids bath time for added safety or soften to a sophisticated glow for a spa-like soak (champagne optional). Whether you want your bath to feel traditional, eclectic, rustic or sleek, there is a pendant persona just right for you!

Ready for your **CLOSE UP?**

In a bathroom, the view is everything! We all need to put our best face forward on a daily basis and that requires seeing clearly with task lighting properly placed by the mirror. A pair of sconces or pendants, mounted at eye level, provide shadowless illumination and is ideal for everyday tasks like shaving, dental hygiene, applying makeup and hairstyling. It's important that these lights not be placed too high, where a bulb can be seen, since the glare may cause eye fatigue.

STANDOUT SELECTIONS FOR EVERY STYLE




PICK OUT THE PERFECT PENDANT
from Hinkley's full offering on pages 27-33 of the pictorial index.

FROM LEFT: BENNETT 5357PN, PAGE 367 | CASA 4017OL-CL, PAGE 267 | MERIDIAN 3877BN, PAGE 195
PLYMOUTH 4247PL, PAGE 280 | ACADEMY 67073OZ, PAGE 88

SIMI™

FINISH BRUSHED NICKEL
GLASS ETCHED WHITE

Minimal in form, Simi makes a strong case for simplicity. Sleek end caps and a center bracelet in Chrome or Brushed Nickel finish options add a seamless finishing touch to the slim profile.

 exclusively available in
HIGH-PERFORMANCE LED

ADDITIONAL FINISHES
Chrome (CM)



59922 BN
5¼" W, 12½" H



59923 BN
5¼" W, 22¾" H
(mounted vertically)



59923 BN
22¾" W, 5¼" H



59924 BN
32¼" W, 5¼" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	INV
59922 BN	17w LED	1250	3000K	92	1-100w	3¾"	9"	4¾" W, 6¾" H	•
59923 BN	33w LED	2450	3000K	92	4-60w	3¾"	2¾"	6¾" W, 4¾" H	•
59924 BN	52w LED	3800	3000K	92	6-60w	3¾"	2¾"	6¾" W, 4¾" H	•

For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

Minimal in form, Simi makes a strong case for simplicity. Sleek end caps and a center bracelet in Chrome or Brushed Nickel finish options add a seamless finishing touch to the slim profile.



FINISH CHROME
GLASS ETCHED WHITE

SIMI™



exclusively available in
HIGH-PERFORMANCE LED 

ADDITIONAL FINISHES
Brushed Nickel (BN)





59923 CM
5¼" W, 22¾" H
(mounted vertically)
 





59922 CM
5¼" W, 12½" H
 



59923 CM
22¾" W, 5¼" H
 



59924 CM
32¼" W, 5¼" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	
59922 CM	17w LED	1250	3000K	92	1-100w	3¾"	9"	4¾" W, 6¾" H	•
59923 CM	33w LED	2450	3000K	92	4-60w	3¾"	2¾"	6¾" W, 4¾" H	•
59924 CM	52w LED	3800	3000K	92	6-60w	3¾"	2¾"	6¾" W, 4¾" H	•

For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

ACCLAIM™

FINISH BRUSHED NICKEL,
POLISHED NICKEL
GLASS ETCHED,
SILK-SCREENED INSIDE

Acclaim is a striking contemporary LED design devoted to modern simplicity. A sleek cylinder of etched tempered glass, silk-screened white along the inside, provides a uniform glow from the soft white eco-efficient LED light source. Simple and elegant die-casted end caps capture the glass shade, attaching it to the full-length back plate. Available in Brushed Nickel or Polished Nickel, the raceway back plate allows mounting directly to the wall without the included junction box cover plate, for a clean and minimal look when mounting vertically or horizontally.



exclusively available in
HIGH-PERFORMANCE LED



53842 PN
16" W, 3" H



53842 BN
3" W, 16" H
(mounted vertically)



53844 PN
29½" W, 3" H*
(shown without junction box cover plate)



53844 BN
29½" W, 3" H



53842 BN
16" W, 3" H*
(shown without junction box cover plate)

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	INV
53842 BN	15w LED	1200	2700K	90	2-60w	3½"**, 3¾"	1½"	16" W, 3" H*	•
53842 PN	15w LED	1200	2700K	90	2-60w	3½"**, 3¾"	1½"	16" W, 3" H*	•
53844 BN	30w LED	2400	2700K	90	4-60w	3½"**, 3¾"	1½"	29½" W, 3" H*	•
53844 PN	30w LED	2400	2700K	90	4-60w	3½"**, 3¾"	1½"	29½" W, 3" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.


Portia's slim profile unifies design and technology. A pair of blown etched opal glass cylinders extends from a center metal fixture body, creating a streamlined cylindrical form. Finished in either Brushed Nickel or Polished Nickel, this eco-efficient linear LED collection is fully dimmable and provides even, warm white light. The raceway back plate and optional junction box cover plate provide multiple mounting opportunities.

FINISH BRUSHED NICKEL,
POLISHED NICKEL
GLASS ETCHED OPAL

PORTIA™

exclusively available in
HIGH-PERFORMANCE LED 



52112 PN
4¾" W, 19" H
(mounted vertically)
  



52112 PN
19" W, 3" H*
(shown without junction box cover plate)
  




52112 PN
19" W, 4¾" H
  



52112 BN
19" W, 3" H*
(shown without junction box cover plate)
  



52112 BN
19" W, 4¾" H
  

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	
52112 BN	15w LED	1200	2700K	90	2-60w	3¼***, 3½"	1½"	6" W, 3" H*	•
52112 PN	15w LED	1200	2700K	90	2-60w	3¼***, 3½"	1½"	6" W, 3" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

UNITY™

FINISH BRUSHED NICKEL,
POLISHED NICKEL
GLASS ETCHED,
SILK-SCREENED INSIDE

Unity's minimalist silhouette artfully combines form and function. A sleek cylinder of etched tempered glass, silk-screened white along the inside, is exquisitely captured on each end with solid die cast brackets precisely formed to match the contour of the glass shade. The eco-efficient linear LED light source provides warm white light and is fully dimmable. Offered in Brushed Nickel or Polished Nickel, a raceway back plate allows mounting directly to the wall without the included junction box cover plate, for a clean and minimal look when mounting vertically or horizontally.



exclusively available in
HIGH-PERFORMANCE LED



55652 PN
15½" W, 3" H*
(shown without junction box cover plate)



55654 PN
29" W, 4¾" H



55652 BN
3" W, 15½" H
(mounted vertically)



55654 BN
29" W, 3" H*
(shown without junction box cover plate)



55652 BN
15½" W, 4¾" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	INV
55652 BN	15w LED	1200	2700K	90	2-60w	3½", 3¾"	1½"	15½" W, 3" H*	•
55652 PN	15w LED	1200	2700K	90	2-60w	3½", 3¾"	1½"	15½" W, 3" H*	•
55654 BN	30w LED	2400	2700K	90	4-60w	3½", 3¾"	1½"	29" W, 3" H*	•
55654 PN	30w LED	2400	2700K	90	4-60w	3½", 3¾"	1½"	29" W, 3" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

Tremont offers a bold silhouette ideal for any transitional décor. The formed linear panel of etched white acrylic creates a soft and seamless appearance while evenly diffusing the eco-efficient LED light source. Offered in Brushed Nickel or Polished Nickel, the shade is secured with sleek metal bands, riveted at each end and framed by a full-length back plate. A raceway back plate allows mounting directly to the wall without the included junction box cover plate, for a more streamlined look.

FINISH BRUSHED NICKEL,
POLISHED NICKEL
GLASS ETCHED WHITE
ACRYLIC

TREMONT™

exclusively available in
HIGH-PERFORMANCE LED 



51812 PN
3½" W, 16" H
(mounted vertically)



51812 PN
16" W, 3½" H*
(shown without junction box cover plate)



51814 PN
29½" W, 4¾" H



51814 BN
29½" W, 3½" H*
(shown without junction box cover plate)



51812 BN
16" W, 4¾" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	INV
51812 BN	15w LED	1200	2700K	90	2-60w	2¾***, 3"	1¾"	16" W, 3½" H*	•
51812 PN	15w LED	1200	2700K	90	2-60w	2¾***, 3"	1¾"	16" W, 3½" H*	•
51814 BN	30w LED	2400	2700K	90	4-60w	2¾***, 3"	1¾"	29½" W, 3½" H*	•
51814 PN	30w LED	2400	2700K	90	4-60w	2¾***, 3"	1¾"	29½" W, 3½" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

FAIRLANE™

FINISH CHROME,
BRUSHED NICKEL
GLASS ETCHED WHITE ACRYLIC

Fairlane features elements of mid-century style updated to contemporary cool. A solid formed metal frame encloses etched white acrylic panels, evenly diffusing the eco-efficient LED light source. The dimmable soft white light complements this retro-inspired design, which is offered in a Brushed Nickel or Chrome finish for a polished appearance. Fairlane may be mounted vertically or horizontally, increasing its versatility.



exclusively available in
HIGH-PERFORMANCE LED



54812 CM
16" W, 5" H



54812 CM
5" W, 16" H
(mounted vertically)



54814 CM
29½" W, 5" H



54814 BN
29½" W, 5" H



54812 BN
16" W, 5" H

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE	INV
54812 BN	15w LED	1200	2700K	90	2-60w	3½"	2½"	16" W, 5" H	•
54812 CM	15w LED	1200	2700K	90	2-60w	3½"	2½"	16" W, 5" H	•
54814 BN	30w LED	2400	2700K	90	4-60w	3½"	2½"	29½" W, 5" H	•
54814 CM	30w LED	2400	2700K	90	4-60w	3½"	2½"	29½" W, 5" H	•

For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.



WINTON™

FINISH BRUSHED NICKEL
GLASS INSIDE WHITE ETCHED PANELS

Winton is a retro-inspired design updated for today's contemporary decors. The heavy, rectangular tube construction has forged details and a unique fitted glass panel design.

ADDITIONAL FINISHES

Chrome (CM)



5421 BN
17" DIA., 7" H



5232 BN
15½" W, 5" H



5234 BN
26¼" W, 5" H



5236 BN
37¼" W, 5" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5232 BN	2-100w Incan. or 2-17w LED Med.	5"	2½"	14½" W, 4¾" H	•
5234 BN	4-100w Incan. or 4-17w LED Med.	5"	2½"	25" W, 5" H	•
5236 BN	6-100w Incan. or 6-17w LED Med.	5"	2½"	36" W, 4¾" H	•
5421 BN*	3-60w Med.				

*Recommended companion flush mount. For additional options, see pages 24-26.

Winton is a retro-inspired design updated for today's contemporary decors. The heavy, rectangular tube construction has forged details and a unique fitted glass panel design.

FINISH CHROME
GLASS INSIDE WHITE ETCHED PANELS

WINTON™


ADDITIONAL FINISHES
Brushed Nickel (BN)



5232 CM
15½" W, 5" H



5421 CM
17" DIA., 7" H



5234 CM
26¼" W, 5" H



5236 CM
37¼" W, 5" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5232 CM	2-100w Incan. or 2-17w LED Med.	5"	2½"	14½" W, 4¾" H	•
5234 CM	4-100w Incan. or 4-17w LED Med.	5"	2½"	25" W, 5" H	•
5236 CM	6-100w Incan. or 6-17w LED Med.	5"	2½"	36" W, 4¾" H	•
5421 CM*	3-60w Med.				

*Recommended companion flush mount. For additional options, see pages 24-26.

MILA™

FINISH CHROME
GLASS ETCHED OPAL

Mila's modern design captivates with sleek symmetry as the elongated shades appear to float next to angled panel transitions to create a seamless form.

ADDITIONAL FINISHES

Brushed Nickel (BN)



5421 CM
17" DIA., 7" H





53552 CM
53552 CM-LED
16" W, 5" H
 





53550 CM
53550 CM-LED
7¾" W, 10" H
 



53553 CM
53553 CM-LED
24" W, 5" H
 



53554 CM
53554 CM-LED
32¼" W, 5" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
53550 CM	1-60w G9*	53550 CM-LED	1-4.5w G9 LED**	4"	5"	7¾" W, 10" H	•
53552 CM	2-60w G9*	53552 CM-LED	2-4.5w G9 LED**	4"	2½"	16" W, 5" H	•
53553 CM	3-60w G9*	53553 CM-LED	3-4.5w G9 LED**	4"	2½"	24" W, 5" H	•
53554 CM	4-60w G9*	53554 CM-LED	4-4.5w G9 LED**	4"	2½"	32¼" W, 5" H	•
5421 CM***							

*G9 halogen bulbs included. **G9 LED bulbs included. ***Recommended companion flush mount. For additional options, see pages 24-26. For complete product details and LED specifications, refer to hinkleylighting.com.

Mila's modern design captivates with sleek symmetry as the elongated shades appear to float next to angled panel transitions to create a seamless form.

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

MILA™

ADDITIONAL FINISHES
Chrome (CM)



53552 BN
53552 BN-LED
16" W, 5" H



5421 BN
17" DIA., 7" H



53553 BN
53553 BN-LED
24" W, 5" H



53550 BN
53550 BN-LED
7¾" W, 10" H



53554 BN
53554 BN-LED
32¼" W, 5" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
53550 BN	1-60w G9*	53550 BN-LED	1-4.5w G9 LED**	4"	5"	7¾" W, 10" H	•
53552 BN	2-60w G9*	53552 BN-LED	2-4.5w G9 LED**	4"	2½"	16" W, 5" H	•
53553 BN	3-60w G9*	53553 BN-LED	3-4.5w G9 LED**	4"	2½"	24" W, 5" H	•
53554 BN	4-60w G9*	53554 BN-LED	4-4.5w G9 LED**	4"	2½"	32¼" W, 5" H	•
5421 BN***	3-60w Med.						

*G9 halogen bulbs included. **G9 LED bulbs included. ***Recommended companion flush mount. For additional options, see pages 24-26. For complete product details and LED specifications, refer to hinkleylighting.com.

DARIA™

FINISH CHROME
GLASS ETCHED OPAL

Daria is a soft contemporary design, making this the perfect complement to any décor. The Chrome finish allows the prominent, etched opal glass shade to create a minimalist style statement. Daria sconces can be mounted horizontally or vertically.



5421 CM
17" DIA., 7" H



55482 CM
16¾" W, 5" H



55483 CM
24" W, 5" H



55482 CM
5" W, 16¾" H
(mounted vertically)



55484 CM
32½" W, 5" H


ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
55482 CM	2-60w G9*	4½"	2½"	16¾" W, 5" H	•
55483 CM	3-60w G9*	4½"	2½"	24" W, 5" H	•
55484 CM	4-60w G9*	4½"	2½"	32½" W, 5" H	•
5421 CM**	3-60w Med.				

*G9 halogen bulbs included. **Recommended companion flush mount. For additional options, see pages 24-26.

Mira's contemporary look is enhanced by its sleek design. Its raceway back plate features a seedy glass panel that adds to its modern appeal. Available in Chrome with etched opal glass, Mira can be mounted vertically or horizontally to maximize versatility. G9 lamps are included.

FINISH CHROME
GLASS ETCHED OPAL

MIRA™



56012 CM
16¼" W, 6" H



5421 CM
17" DIA., 7" H



56012 CM
6" W, 16¼" H
(mounted vertically)



56010 CM
6" W, 16¼" H



56013 CM
24¾" W, 6" H



56014 CM
33½" W, 6" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
56010 CM	1-60w G9*	3½"	8¼"	6" W, 16¼" H	•
56012 CM	2-60w G9*	3½"	3"	16¼" W, 6" H	•
56013 CM	3-60w G9*	3½"	3"	24¾" W, 6" H	•
56014 CM	4-60w G9*	3½"	3"	33½" W, 6" H	•
5421 CM**	3-60w Med.				

*G9 halogen bulbs included. **Recommended companion flush mount. For additional options, see pages 24-26.



Daphne features contemporary pocket style bubble art glass set against a sleek raceway back plate in chic Chrome, Brushed Nickel or Brushed Bronze finishes. The etched bottom lens conceals the light source.

FINISH CHROME
GLASS ETCHED BUBBLE ART

DAPHNE™

ADDITIONAL FINISHES
Brushed Bronze (BR), Brushed Nickel (BN)



5923 CM
5923 CM-LED2
24" W, 5" H
T24



5922 CM
5922 CM-LED2
16" W, 5" H
T24



5924 CM
5924 CM-LED2
32" W, 5" H
T24



5920 CM
5920 CM-LED2**
8½" W, 9" H
T24



5925 CM
5925 CM-LED2
40" W, 5" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
5920 CM	1-75w Med.	5920 CM-LED2**	17w LED	600	2700K	97	1-60w	4", 4¼"***	4½"	8½" W, 9" H
5922 CM	2-60w G9*	5922 CM-LED2	14w LED	1200	2700K	97	2-60w	3¾", 4"***	2½"	16" W, 5" H
5923 CM	3-60w G9*	5923 CM-LED2	21w LED	1800	2700K	97	3-60w	3¾", 4"***	2½"	24" W, 5" H
5924 CM	4-60w G9*	5924 CM-LED2	28w LED	2400	2700K	97	4-60w	3¾", 4"***	2½"	32" W, 5" H
5925 CM	5-60w G9*	5925 CM-LED2	35w LED	3000	2700K	97	5-60w	3¾", 4"***	2½"	40" W, 5" H

*G9 halogen bulbs included. **5920 CM-LED2 is not ADA compliant. ***Extension for -LED2 item. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

DAPHNE™

FINISH BRUSHED NICKEL
GLASS ETCHED BUBBLE ART

Daphne features contemporary pocket style bubble art glass set against a sleek raceway back plate in chic Chrome, Brushed Nickel or Brushed Bronze finishes. The etched bottom lens conceals the light source.

ADDITIONAL FINISHES

Brushed Bronze (BR), Chrome (CM)



5922 BN
5922 BN-LED2
16" W, 5" H



5923 BN
5923 BN-LED2
24" W, 5" H



5920 BN
5920 BN-LED2**
8½" W, 9" H



5924 BN
5924 BN-LED2
32" W, 5" H



5925 BN
5925 BN-LED2
40" W, 5" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
5920 BN	1-75w Med.	5920 BN-LED2**	17w LED	600	2700K	97	1-60w	4", 4¼"***	4½"	8½" W, 9" H
5922 BN	2-60w G9*	5922 BN-LED2	14w LED	1200	2700K	97	2-60w	3¾", 4"***	2½"	16" W, 5" H
5923 BN	3-60w G9*	5923 BN-LED2	21w LED	1800	2700K	97	3-60w	3¾", 4"***	2½"	24" W, 5" H
5924 BN	4-60w G9*	5924 BN-LED2	28w LED	2400	2700K	97	4-60w	3¾", 4"***	2½"	32" W, 5" H
5925 BN	5-60w G9*	5925 BN-LED2	35w LED	3000	2700K	97	5-60w	3¾", 4"***	2½"	40" W, 5" H

*G9 halogen bulbs included. **5920 CM-LED2 is not ADA compliant. ***Extension for -LED2 item. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

Daphne features contemporary pocket style bubble art glass set against a sleek raceway back plate in chic Chrome, Brushed Nickel or Brushed Bronze finishes. The etched bottom lens conceals the light source.

FINISH BRUSHED BRONZE
GLASS AMBER ETCHED BUBBLE ART

DAPHNE™

ADDITIONAL FINISHES
Brushed Nickel (BN), Chrome (CM)



5923 BR
24" W, 5" H



5922 BR
16" W, 5" H



5924 BR
32" W, 5" H



5920 BR
8½" W, 9" H



5925 BR
40" W, 5" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5920 BR	1-75w Med.	4"	4½"	8½" W, 9" H
5922 BR	2-60w G9*	3¾"	2½"	16" W, 5" H
5923 BR	3-60w G9*	3¾"	2½"	24" W, 5" H
5924 BR	4-60w G9*	3¾"	2½"	32" W, 5" H
5925 BR	5-60w G9*	3¾"	2½"	40" W, 5" H

*G9 halogen bulbs included. For flush mount options, see pages 24-26.

CHLOE™

FINISH BRUSHED NICKEL
GLASS PIASTRA

Chloe is a dramatic modern design with stunning Piastra glass as its focal point. A slender Brushed Nickel frame securely captures the glass allowing this versatile collection to be mounted horizontally or vertically.



52402 BN
8" W, 17" H
(mounted vertically)



52400 BN
8½" W, 8" H



52402 BN
17" W, 8" H



52403 BN
24¾" W, 8" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
52400 BN	1-60w G9*	4"	4¼"	6½" W, 4¾" H	•
52402 BN	2-60w G9*	4"	4"	14¼" W, 4¾" H	•
52403 BN	3-60w G9*	4"	4"	22" W, 4¾" H	•

*G9 halogen bulbs included. For flush mount options, see pages 24-26.

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the subtle, split fork frames add understated architectural style.

Latitude Interior, pages 198-199

FINISH CHROME
GLASS CLEAR BEVELED INSIDE-ETCHED

LATITUDE™

ADDITIONAL FINISHES
Brushed Nickel (BN), Oil Rubbed Bronze (OZ)



5652 CM
5652 CM-LED2
18" W, 5¾" H



5650 CM
5650 CM-LED2
5" W, 8" H



5654 CM
5654 CM-LED2
26" W, 5¾" H



5651 CM
5½" W, 21½" H



5656 CM
5656 CM-LED2
37½" W, 5¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE	INV
5650 CM	1-60w G9*	5650 CM-LED2	7w LED	600	2700K	97	1-60w	3½***, 4"	4"	5" W, 8" H	•
5651 CM	2-100w Med.							5½"	10¾"	5½" W, 21½" H	
5652 CM	2-60w G9*	5652 CM-LED2	14w LED	1200	2700K	97	2-60w	3½***, 4"	¾"	17" W, 4¾" H	•
5654 CM	4-60w G9*	5654 CM-LED2	28w LED	2400	2700K	97	4-60w	3½***, 4"	¾"	25" W, 4¾" H	•
5656 CM	6-60w G9*	5656 CM-LED2	42w LED	3600	2700K	97	6-60w	3½***, 4"	¾"	36¾" W, 4¾" H	•

*G9 halogen bulbs included. **Extension for -LED2 item. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

LATITUDE™

FINISH BRUSHED NICKEL
GLASS CLEAR BEVELED INSIDE-ETCHED

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the subtle, split fork frames add understated architectural style.

Latitude Interior, pages 198-199

ADDITIONAL FINISHES

Chrome (CM), Oil Rubbed Bronze (OZ)



5651 BN
5½" W, 21½" H



5650 BN
5650 BN-LED2
5" W, 8" H
T24 ♿



5652 BN
5652 BN-LED2
18" W, 5¾" H
T24 ♿



5654 BN
5654 BN-LED2
26" W, 5¾" H
T24 ♿



5656 BN
5656 BN-LED2
37½" W, 5¾" H
T24 ♿

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE	INV
5650 BN	1-60w G9*	5650 BN-LED2	7w LED	600	2700K	97	1-60w	3½"**, 4"	4"	5" W, 8" H	•
5651 BN	2-100w Med.							5½"	10¾"	5½" W, 21½" H	
5652 BN	2-60w G9*	5652 BN-LED2	14w LED	1200	2700K	97	2-60w	3½"**, 4"	3¼"	17" W, 4¾" H	•
5654 BN	4-60w G9*	5654 BN-LED2	28w LED	2400	2700K	97	4-60w	3½"**, 4"	3¼"	25" W, 4¾" H	•
5656 BN	6-60w G9*	5656 BN-LED2	42w LED	3600	2700K	97	6-60w	3½"**, 4"	3¼"	36¼" W, 4¾" H	•

*G9 halogen bulbs included. **Extension for -LED2 item. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

Latitude is contemporary and sleek, finding its true beauty in the minimalist design. The slim glass panel features rectangular etching while the subtle, split fork frames add understated architectural style.

Latitude Interior, pages 198-199

FINISH OIL RUBBED BRONZE
GLASS CLEAR BEVELED INSIDE-ETCHED

LATITUDE™

ADDITIONAL FINISHES
Brushed Nickel (BN), Chrome (CM)



5652 OZ
5652 OZ-LED2
18" W, 5¾" H
• T24 ♿



5650 OZ
5650 OZ-LED2
5" W, 8" H
• T24 ♿



5654 OZ
5654 OZ-LED2
26" W, 5¾" H
• T24 ♿



5651 OZ
5½" W, 21½" H



5656 OZ
5656 OZ-LED2
37½" W, 5¾" H
• T24 ♿

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE	INV
5650 OZ	1-60w G9*	5650 OZ-LED2	7w LED	600	2700K	97	1-60w	3½***, 4"	4"	5" W, 8" H	•
5651 OZ	2-100w Med.							5½"	10¾"	5½" W, 21½" H	
5652 OZ	2-60w G9*	5652 OZ-LED2	14w LED	1200	2700K	97	2-60w	3½***, 4"	¾"	17" W, 4¾" H	•
5654 OZ	4-60w G9*	5654 OZ-LED2	28w LED	2400	2700K	97	4-60w	3½***, 4"	¾"	25" W, 4¾" H	•
5656 OZ	6-60w G9*	5656 OZ-LED2	42w LED	3600	2700K	97	6-60w	3½***, 4"	¾"	36¾" W, 4¾" H	•

*G9 halogen bulbs included. **Extension for -LED2 item. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

VERVE™

FINISH CHROME
GLASS ETCHED OPAL

Catch a wave with Verve's contemporary silhouette. Individual curved cast fitters support the modern etched opal glass while mimicking the sleek contours of the bar. A crisp Chrome finish balances the unique, undulating design.



51102 CM
51102 CM-LED
15½" W, 4¾" H



51100 CM
51100 CM-LED
6¾" W, 7¼" H



51103 CM
51103 CM-LED
24" W, 4¾" H



51104 CM
51104 CM-LED
32¾" W, 4¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
51100 CM	1-60w G9*	51100 CM-LED	1-4.5w G9 LED**	4¾"	3¾"	4¾" W, 7¼" H	•
51102 CM	2-60w G9*	51102 CM-LED	2-4.5w G9 LED**	4¾"	2½"	11" W, 4¾" H	•
51103 CM	3-60w G9*	51103 CM-LED	3-4.5w G9 LED**	4¾"	2½"	11" W, 4¾" H	•
51104 CM	4-60w G9*	51104 CM-LED	4-4.5w G9 LED**	4¾"	2½"	11" W, 4¾" H	•

*G9 halogen bulbs included. **G9 LED bulbs included. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

Lanza features contemporary styling with geometric patterns that are emphasized in Antique Nickel, Brushed Bronze and Buckeye Bronze finishes. The elongated oval, etched opal glass reinforces its sleek design.

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL

LANZA™


ADDITIONAL FINISHES
Brushed Bronze (BR), Buckeye Bronze (KZ)




5100 AN
5100 AN-LED
7¼" W, 12" H





5103 AN
5103 AN-LED
25" W, 6¾" H





5102 AN
5102 AN-LED
16¼" W, 6¾" H




5104 AN
5104 AN-LED
34" W, 6¾" H




5105 AN
5105 AN-LED
43" W, 6¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5100 AN	1-60w G9*	5100 AN-LED	1-4.5w G9 LED**	5"	6½"	4¾" W, 12" H	
5102 AN	2-60w G9*	5102 AN-LED	2-4.5w G9 LED**	5"	4"	9" W, 4¾" H	•
5103 AN	3-60w G9*	5103 AN-LED	3-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•
5104 AN	4-60w G9*	5104 AN-LED	4-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•
5105 AN	5-60w G9*	5105 AN-LED	5-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•

*G9 halogen bulbs included. **G9 LED bulbs included. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

LANZA™

FINISH BUCKEYE BRONZE
GLASS ETCHED OPAL

Lanza features contemporary styling with geometric patterns that are emphasized in Antique Nickel, Brushed Bronze and Buckeye Bronze finishes. The elongated oval, etched opal glass reinforces its sleek design.

ADDITIONAL FINISHES

Antique Nickel (AN), Brushed Bronze (BR)



5103 KZ
5103 KZ-LED
25" W, 6¾" H



5100 KZ
5100 KZ-LED
7¼" W, 12" H



5104 KZ
5104 KZ-LED
34" W, 6¾" H



5102 KZ
5102 KZ-LED
16¼" W, 6¾" H



5105 KZ
5105 KZ-LED
43" W, 6¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5100 KZ	1-60w G9*	5100 KZ-LED	1-4.5w G9 LED**	5"	6½"	4¾" W, 12" H	
5102 KZ	2-60w G9*	5102 KZ-LED	2-4.5w G9 LED**	5"	4"	9" W, 4¾" H	•
5103 KZ	3-60w G9*	5103 KZ-LED	3-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•
5104 KZ	4-60w G9*	5104 KZ-LED	4-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•
5105 KZ	5-60w G9*	5105 KZ-LED	5-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•

*G9 halogen bulbs included. **G9 LED bulbs included. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

Lanza features contemporary styling with geometric patterns that are emphasized in Antique Nickel, Brushed Bronze and Buckeye Bronze finishes. The elongated oval, etched opal glass reinforces its sleek design.

FINISH BRUSHED BRONZE
GLASS ETCHED OPAL

LANZA™

ADDITIONAL FINISHES
Antique Nickel (AN), Buckeye Bronze (KZ)



5100 BR
5100 BR-LED
7¼" W, 12" H



5103 BR
5103 BR-LED
25" W, 6¾" H



5421 BR
17" DIA., 7" H



5102 BR
5102 BR-LED
16¼" W, 6¾" H



5104 BR
5104 BR-LED
34" W, 6¾" H



5105 BR
5105 BR-LED
43" W, 6¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5100 BR	1-60w G9*	5100 BR-LED	1-4.5w G9 LED**	5"	6½"	4¾" W, 12" H	
5102 BR	2-60w G9*	5102 BR-LED	2-4.5w G9 LED**	5"	4"	9" W, 4¾" H	•
5103 BR	3-60w G9*	5103 BR-LED	3-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•
5104 BR	4-60w G9*	5104 BR-LED	4-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•
5105 BR	5-60w G9*	5105 BR-LED	5-4.5w G9 LED**	5"	4"	12" W, 4¾" H	•
5421 BR***	3-60w Med.						

*G9 halogen bulbs included. **G9 LED bulbs included. ***Recommended companion flush mount. For additional options, see pages 24-26. For complete product details and LED specifications, refer to hinkleylighting.com.

TAYLOR™

FINISH BRUSHED NICKEL
GLASS ETCHED WHITE

Taylor's modern silhouette highlights its tapered rectangular etched white glass in Chrome, Brushed Nickel or Buckeye Bronze finishes.

ADDITIONAL FINISHES

Buckeye Bronze (KZ), Chrome (CM)



5023 BN
5023 BN-LED
27½" W, 6" H



5551 BN
15" DIA., 7¾" H



5022 BN
5022 BN-LED
18¾" W, 6" H



5024 BN
5024 BN-LED
36¼" W, 6" H



5020 BN
5020 BN-LED
7¾" W, 6" H



5025 BN
5025 BN-LED
45" W, 7" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5020 BN	1-60w G9*	5020 BN-LED	1-4.5w G9 LED**	5¼"	3¾"	7¾" W, 4¾" H	
5022 BN	2-60w G9*	5022 BN-LED	2-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5023 BN	3-60w G9*	5023 BN-LED	3-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5024 BN	4-60w G9*	5024 BN-LED	4-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5025 BN	5-60w G9*	5025 BN-LED	5-4.5w G9 LED**	5½"	4½"	12" W, 4¾" H	•
5551 BN***	2-60w Med.						

*G9 bulbs included. **G9 LED bulbs included. *** Recommended companion flush mount. For additional options, see pages 24-26. For complete product details and LED specifications, refer to hinkleylighting.com.

Taylor's modern silhouette highlights its tapered rectangular etched white glass in Chrome, Brushed Nickel or Buckeye Bronze finishes.

FINISH CHROME
GLASS ETCHED WHITE

TAYLOR™

ADDITIONAL FINISHES
Brushed Nickel (BN), Buckeye Bronze (KZ)



5551 CM
15" DIA., 7¾" H



5023 CM
5023 CM-LED
27½" W, 6" H



5024 CM
5024 CM-LED
36¼" W, 6" H



5022 CM
5022 CM-LED
18¾" W, 6" H



5025 CM
5025 CM-LED
45" W, 7" H



5020 CM
5020 CM-LED
7¾" W, 6" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5020 CM	1-60w G9*	5020 CM-LED	1-4.5w G9 LED**	5¼"	3¾"	7¾" W, 4¾" H	
5022 CM	2-60w G9*	5022 CM-LED	2-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5023 CM	3-60w G9*	5023 CM-LED	3-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5024 CM	4-60w G9*	5024 CM-LED	4-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5025 CM	5-60w G9*	5025 CM-LED	5-4.5w G9 LED**	5½"	4½"	12" W, 4¾" H	•
5551 CM***	2-60w Med.						

*G9 bulbs included. **G9 LED bulbs included. *** Recommended companion flush mount. For additional options, see pages 24-26. For complete product details and LED specifications, refer to hinkleylighting.com.

TAYLOR™

FINISH BUCKEYE BRONZE
GLASS ETCHED WHITE

Taylor's modern silhouette highlights its tapered rectangular etched white glass in Chrome, Brushed Nickel or Buckeye Bronze finishes.

ADDITIONAL FINISHES

Brushed Nickel (BN), Chrome (CM)



5023 KZ
5023 KZ-LED
27½" W, 6" H




5020 KZ
5020 KZ-LED
7¾" W, 6" H



5022 KZ
5022 KZ-LED
18¾" W, 6" H



5024 KZ
5024 KZ-LED
36¼" W, 6" H



5025 KZ
5025 KZ-LED
45" W, 7" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5020 KZ	1-60w G9*	5020 KZ-LED	1-4.5w G9 LED**	5¼"	3¾"	7¾" W, 4¾" H	
5022 KZ	2-60w G9*	5022 KZ-LED	2-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5023 KZ	3-60w G9*	5023 KZ-LED	3-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5024 KZ	4-60w G9*	5024 KZ-LED	4-4.5w G9 LED**	5½"	3¾"	7¾" W, 4¾" H	
5025 KZ	5-60w G9*	5025 KZ-LED	5-4.5w G9 LED**	5½"	4½"	12" W, 4¾" H	•

*G9 halogen bulbs included. **G9 LED bulbs included. For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

Avon's updated traditional style features a clean, minimalist design with cast detailing. Available in Chrome, Brushed Nickel and Buckeye Bronze finishes.

FINISH BUCKEYE BRONZE
GLASS ETCHED OPAL

AVON™

ADDITIONAL FINISHES
Brushed Nickel (BN), Chrome (CM),
Chrome with Clear Seedy glass (CM-CL)



5553 KZ
5553 KZ-LED
23" W, 8" H



5550 KZ
5550 KZ-LED
7¼" W, 7½" H



5554 KZ
5554 KZ-LED
31¾" W, 8" H



5552 KZ
5552 KZ-LED
14½" W, 8" H



5555 KZ
40¼" W, 8" H



5556 KZ
48" W, 8" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
5550 KZ	1-100w Med.	5550 KZ-LED	1-15w LED	900	2700K	90	1-75w	6¼"	5¼"	7¼" W, 4½" H
5552 KZ	2-100w Med.	5552 KZ-LED	2-15w LED	1800	2700K	90	2-75w	6¼"	5¾"	7¼" W, 4½" H
5553 KZ	3-100w Med.	5553 KZ-LED	3-15w LED	2700	2700K	90	3-75w	6¼"	5¾"	7¼" W, 4½" H
5554 KZ	4-100w Med.	5554 KZ-LED	4-15w LED	3600	2700K	90	4-75w	6¼"	5¾"	7¼" W, 4½" H
5555 KZ	5-100w Med.							6¼"	5¾"	18¼" W, 4½" H
5556 KZ	6-100w Med.							6¼"	5¾"	18¼" W, 4½" H

For complete product details and LED specifications, refer to hinkleylighting.com. For flush mount options, see pages 24-26.

AVON™

FINISH CHROME
GLASS CLEAR SEEDY

Avon's updated traditional style features a clean, minimalist design with cast detailing. Available in Chrome, Brushed Nickel and Buckeye Bronze finishes.

ADDITIONAL FINISHES

Brushed Nickel (BN),
Buckeye Bronze (KZ), Chrome (CM)



5550 CM-CL
7¼" W, 7½" H



5553 CM-CL
23" W, 8" H



5552 CM-CL
14½" W, 8" H



5554 CM-CL
31¾" W, 8" H



5555 CM-CL
40¼" W, 8" H



5556 CM-CL
48" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5550 CM-CL	1-100w Med.	6¼"	5¼"	7¼" W, 4½" H
5552 CM-CL	2-100w Med.	6¼"	5¾"	7¼" W, 4½" H
5553 CM-CL	3-100w Med.	6¼"	5¾"	7¼" W, 4½" H
5554 CM-CL	4-100w Med.	6¼"	5¾"	7¼" W, 4½" H
5555 CM-CL	5-100w Med.	6¼"	5¾"	18¼" W, 4½" H
5556 CM-CL	6-100w Med.	6¼"	5¾"	18¼" W, 4½" H

For flush mount options, see pages 24-26.

Avon's updated traditional style features a clean, minimalist design with cast detailing. Available in Chrome, Brushed Nickel and Buckeye Bronze finishes.

FINISH CHROME
GLASS ETCHED OPAL,
CASED OPAL

AVON™

ADDITIONAL FINISHES
Brushed Nickel (BN), Buckeye Bronze (KZ),
Chrome with Clear Seedy glass (CM-CL)



5553 CM
5553 CM-LED
23" W, 8" H
T24



5550 CM
5550 CM-LED
7¼" W, 7½" H
T24



5551 CM
15" DIA., 7¾" H



5554 CM
5554 CM-LED
31¾" W, 8" H
T24



5552 CM
5552 CM-LED
14½" W, 8" H
T24



5555 CM
40¼" W, 8" H



5556 CM
48" W, 8" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
5550 CM	1-100w Med.	5550 CM-LED	1-15w LED	900	2700K	90	1-75w	6¼"	5¼"	7¼" W, 4½" H
5551 CM	2-60w Med.									
5552 CM	2-100w Med.	5552 CM-LED	2-15w LED	1800	2700K	90	2-75w	6¼"	5¾"	7¼" W, 4½" H
5553 CM	3-100w Med.	5553 CM-LED	3-15w LED	2700	2700K	90	3-75w	6¼"	5¾"	7¼" W, 4½" H
5554 CM	4-100w Med.	5554 CM-LED	4-15w LED	3600	2700K	90	4-75w	6¼"	5¾"	7¼" W, 4½" H
5555 CM	5-100w Med.							6¼"	5¾"	18¼" W, 4½" H
5556 CM	6-100w Med.							6¼"	5¾"	18¼" W, 4½" H

For complete product details and LED specifications, refer to hinkleylighting.com.



ADDITIONAL FINISHES

Buckeye Bronze (KZ), Chrome (CM),
Chrome with Clear Seedy glass (CM-CL)





5551 BN
15" DIA., 7¾" H



5550 BN
5550 BN-LED
7¼" W, 7½" H
 





5553 BN
5553 BN-LED
23" W, 8" H
 



5552 BN
5552 BN-LED
14½" W, 8" H
 



5554 BN
5554 BN-LED
31¾" W, 8" H
 



5555 BN
40¼" W, 8" H



5556 BN
48" W, 8" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
5550 BN	1-100w Med.	5550 BN-LED	1-15w LED	900	2700K	90	1-75w	6¼"	5¼"	7¼" W, 4½" H
5551 BN	2-60w Med.									
5552 BN	2-100w Med.	5552 BN-LED	2-15w LED	1800	2700K	90	2-75w	6¼"	5¾"	7¼" W, 4½" H
5553 BN	3-100w Med.	5553 BN-LED	3-15w LED	2700	2700K	90	3-75w	6¼"	5¾"	7¼" W, 4½" H
5554 BN	4-100w Med.	5554 BN-LED	4-15w LED	3600	2700K	90	4-75w	6¼"	5¾"	7¼" W, 4½" H
5555 BN	5-100w Med.							6¼"	5¾"	18¼" W, 4½" H
5556 BN	6-100w Med.							6¼"	5¾"	18¼" W, 4½" H

For complete product details and LED specifications, refer to hinkleylighting.com.

Tessa's dynamic details exude quality. The precision die-cast back plate, arm and cup combine with a sturdy cross bar to balance its square etched opal glass shades. The ultimate touch: a luxurious Chrome finish that radiates with transitional sophistication.

FINISH CHROME
GLASS ETCHED OPAL

TESSA™



57132 CM
13" W, 7¾" H



5421 CM
17" DIA., 7" H



57133 CM
22" W, 7¾" H



57130 CM
5¾" W, 7¾" H



57134 CM
31" W, 7¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
57130 CM	1-100w Incan. or 1-17w LED Med.	5¾"	4¾"	5¾" Square	•
57132 CM	2-100w Incan. or 2-17w LED Med.	6½"	4¾"	5¾" Square	•
57133 CM	3-100w Incan. or 3-17w LED Med.	6½"	4¾"	5¾" Square	•
57134 CM	4-100w Incan. or 4-17w LED Med.	6½"	4¾"	5¾" Square	•
5421 CM*	3-60w Med.				

*Recommended companion flush mount. For additional options, see pages 24-26.

MILEY™

FINISH CHROME
GLASS CASED OPAL

Miley's chic design complements a variety of decors with its sleek lines and elegant glass shape. The cast stepped back plate and cast glass holders in Chrome or Brushed Nickel finishes add to its beauty.

ADDITIONAL FINISHES

Brushed Nickel (BN)



5421 CM
17" DIA., 7" H



5052 CM
5052 CM-LED
13" W, 6¼" H



5050 CM
5052 CM-LED
4½" W, 6½" H



5053 CM
5053 CM-LED
21½" W, 6¼" H



5054 CM
5054 CM-LED
30" W, 6¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
5050 CM	1-60w G9*	5050 CM-LED	1-5w G9 LED**	5¼"	3¼"	4½" W, 6½" H
5052 CM	2-60w G9*	5052 CM-LED	2-5w G9 LED**	5½"	4"	6½" W, 4½" H
5053 CM	3-60w G9*	5053 CM-LED	3-5w G9 LED**	5½"	4"	6½" W, 4½" H
5054 CM	4-60w G9*	5054 CM-LED	4-5w G9 LED**	5½"	4"	6½" W, 4½" H
5421 CM***	3-60w Med.					

*G9 halogen bulbs included. **G9 LED bulbs included. ***Recommended companion flush mount. For additional options, see pages 24-26. For complete product details and LED specifications, refer to hinkleylighting.com.

Miley's chic design complements a variety of decors with its sleek lines and elegant glass shape. The cast stepped back plate and cast glass holders in Chrome or Brushed Nickel finishes add to its beauty.

FINISH BRUSHED NICKEL
GLASS WHITE ETCHED

MILEY™

ADDITIONAL FINISHES
Chrome (CM)



5052 BN
5052 BN-LED
13" W, 6¼" H



5421 BN
17" DIA., 7" H



5053 BN
5053 BN-LED
21½" W, 6¼" H



5050 BN
5050 BN-LED
4½" W, 6½" H



5054 BN
5054 BN-LED
30" W, 6¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
5050 BN	1-60w G9*	5050 BN-LED	1-5w G9 LED**	5/4"	3/4"	4½" W, 6½" H
5052 BN	2-60w G9*	5052 BN-LED	2-5w G9 LED**	5½"	4"	6½" W, 4½" H
5053 BN	3-60w G9*	5053 BN-LED	3-5w G9 LED**	5½"	4"	6½" W, 4½" H
5054 BN	4-60w G9*	5054 BN-LED	4-5w G9 LED**	5½"	4"	6½" W, 4½" H
5421 BN***	3-60w Med.					

*G9 halogen bulbs included. **G9 LED bulbs included. ***Recommended companion flush mount. For additional options, see pages 24-26. For complete product details and LED specifications, refer to hinkleylighting.com.

KYRA™

FINISH POLISHED NICKEL
GLASS ETCHED OPAL

Clean and crisp, Kyra's minimalist design is anchored with a bold yet simple aesthetic. The sleek cross bar ends with a subtle curve for an element of softness. Rich finish options of Brushed Nickel or Polished Nickel complement the elegant etched opal glass.

ADDITIONAL FINISHES

Brushed Nickel (BN)



55022 PN
14" W, 7¾" H



55020 PN
4¾" W, 7¾" H



55023 PN
24" W, 7¾" H



55024 PN
30" W, 7¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
55020 PN	1-100w Incan. or 1-17w LED Med.	5¼"	4¼"	4¾" W, 7" H	•
55022 PN	2-100w Incan. or 2-17w LED Med.	5¼"	5½"	7" W, 4¾" H	•
55023 PN	3-100w Incan. or 3-17w LED Med.	5¼"	5½"	7" W, 4¾" H	•
55024 PN	4-100w Incan. or 4-17w LED Med.	5¼"	5½"	7" W, 4¾" H	•

For flush mount options, see pages 24-26.

Clean and crisp, Kyra's minimalist design is anchored with a bold yet simple aesthetic. The sleek cross bar ends with a subtle curve for an element of softness. Rich finish options of Brushed Nickel or Polished Nickel complement the elegant etched opal glass.

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

KYRA™

ADDITIONAL FINISHES
Polished Nickel (PN)



55022 BN
14" W, 7¾" H



5421 BN
17" DIA., 7" H



55023 BN
24" W, 7¾" H



55020 BN
4¾" W, 7¾" H



55024 BN
30" W, 7¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
55020 BN	1-100w Incan. or 1-17w LED Med.	5¼"	4¼"	4¾" W, 7" H	•
55022 BN	2-100w Incan. or 2-17w LED Med.	5¼"	5½"	7" W, 4¾" H	•
55023 BN	3-100w Incan. or 3-17w LED Med.	5¼"	5½"	7" W, 4¾" H	•
55024 BN	4-100w Incan. or 4-17w LED Med.	5¼"	5½"	7" W, 4¾" H	•
5421 BN*	3-60w Med.				

*Recommended companion flush mount. For additional options, see pages 24-26.

KARLIE™

FINISH CHROME
GLASS ETCHED OPAL

Karlie's clean design is transitional in style and will complement a variety of décor. Featuring precision die-cast cups and cylindrical, etched opal glass, it is available in Brushed Nickel and Chrome.

ADDITIONAL FINISHES

Brushed Nickel (BN)



5421 CM
17" DIA., 7" H



54622 CM
13¼" W, 7½" H



54620 CM
4½" W, 8¼" H



54623 CM
22½" W, 7½" H



54624 CM
32" W, 7½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
54620 CM	1-100w Incan. or 1-17w LED Med.	6"	4¾"	4½" W, 7¼" H	•
54622 CM	2-100w Incan. or 2-17w LED Med.	6"	5½"	7¼" W, 4½" H	•
54623 CM	3-100w Incan. or 3-17w LED Med.	6"	5½"	7¼" W, 4½" H	•
54624 CM	4-100w Incan. or 4-17w LED Med.	6"	5½"	7¼" W, 4½" H	•
5421 CM*	3-60w Med.				

*Recommended companion flush mount. For additional options, see pages 24-26.

Karlie's clean design is transitional in style and will complement a variety of décor. Featuring precision die-cast cups and cylindrical, etched opal glass, it is available in Brushed Nickel and Chrome.

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

KARLIE™

ADDITIONAL FINISHES
Chrome (CM)



54622 BN
13¼" W, 7½" H



5421 BN
17" DIA., 7" H



54623 BN
22½" W, 7½" H



54620 BN
4½" W, 8¼" H



54624 BN
32" W, 7½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
54620 BN	1-100w Incan. or 1-17w LED Med.	6"	4¾"	4½" W, 7¼" H	•
54622 BN	2-100w Incan. or 2-17w LED Med.	6"	5½"	7¼" W, 4½" H	•
54623 BN	3-100w Incan. or 3-17w LED Med.	6"	5½"	7¼" W, 4½" H	•
54624 BN	4-100w Incan. or 4-17w LED Med.	6"	5½"	7¼" W, 4½" H	•
5421 BN*	3-60w Med.				

*Recommended companion flush mount. For additional options, see pages 24-26.

LAUREL™

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

Laurel's appealing form combines both traditional and transitional design elements. This collection is available in Polished Nickel or Brushed Nickel, and features etched opal glass shades and medium base lamping. Chic details such as a precision die-cast cross reminiscent of a timeless faucet handle and a cast stepped back plate convey a lasting elegance.

ADDITIONAL FINISHES

Polished Nickel (PN)



5421 BN
17" DIA., 7" H



57552 BN
13" W, 8" H



57550 BN
5" W, 8¼" H



57553 BN
19½" W, 8" H



57554 BN
27¾" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
57550 BN	1-100w Incan. or 1-17w LED Med.	5"	5"	5" W, 6¾" H
57552 BN	2-100w Incan. or 2-17w LED Med.	5"	5½"	6¾" W, 5" H
57553 BN	3-100w Incan. or 3-17w LED Med.	5"	5½"	6¾" W, 5" H
57554 BN	4-100w Incan. or 4-17w LED Med.	5"	5½"	6¾" W, 5" H
5421 BN*	3-60w Med.			

*Recommended companion flush mount. For additional options, see pages 24-26.

Laurel's appealing form combines both traditional and transitional design elements. This collection is available in Polished Nickel or Brushed Nickel, and features etched opal glass shades and medium base lamping. Chic details such as a precision die-cast cross reminiscent of a timeless faucet handle and a cast stepped back plate convey a lasting elegance.

FINISH POLISHED NICKEL
GLASS ETCHED OPAL

LAUREL™

ADDITIONAL FINISHES
Brushed Nickel (BN)



57552 PN
13" W, 8" H



57553 PN
19½" W, 8" H



57550 PN
5" W, 8¼" H



57554 PN
27¾" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
57550 PN	1-100w Incan. or 1-17w LED Med.	5"	5"	5" W, 6¾" H
57552 PN	2-100w Incan. or 2-17w LED Med.	5"	5½"	6¾" W, 5" H
57553 PN	3-100w Incan. or 3-17w LED Med.	5"	5½"	6¾" W, 5" H
57554 PN	4-100w Incan. or 4-17w LED Med.	5"	5½"	6¾" W, 5" H

For flush mount options, see pages 24-26.

PINNACLE™

FINISH ANTIQUE NICKEL
GLASS CLEAR ETCHED

Pinnacle features softly curved mounting bars with cast square decorative medallions in an Antique Nickel finish with clear etched glass.

ADDITIONAL FINISHES

Chrome (CM)



5250 AN
5" W, 9" H



5253 AN
21" W, 7¾" H



5254 AN
29" W, 7¾" H



5252 AN
14" W, 7¾" H



5255 AN
37" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5250 AN	1-100w Incan. or 1-17w LED Med.	7"	4½"	4½" W, 9" H
5252 AN	2-100w Incan. or 2-17w LED Med.	6"	5½"	7" W, 4½" H
5253 AN	3-100w Incan. or 3-17w LED Med.	7"	5½"	9" W, 4½" H
5254 AN	4-100w Incan. or 4-17w LED Med.	7"	5½"	9" W, 4½" H
5255 AN	5-100w Incan. or 5-17w LED Med.	7¼"	5¾"	9¼" W, 4½" H

For flush mount options, see pages 24-26.

Pinnacle features softly curved mounting bars with cast square decorative medallions in a Chrome finish with Antique Nickel accents and etched opal glass.

FINISH CHROME
GLASS ETCHED OPAL

PINNACLE™

ADDITIONAL FINISHES
Antique Nickel (AN)



5253 CM
21" W, 7¾" H



5250 CM
5" W, 9" H



5252 CM
14" W, 7¾" H



5254 CM
29" W, 7¾" H



5255 CM
37" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5250 CM	1-100w Incan. or 1-17w LED Med.	7"	4½"	4½" W, 9" H
5252 CM	2-100w Incan. or 2-17w LED Med.	6"	5½"	7" W, 4½" H
5253 CM	3-100w Incan. or 3-17w LED Med.	7"	5½"	9" W, 4½" H
5254 CM	4-100w Incan. or 4-17w LED Med.	7"	5½"	9" W, 4½" H
5255 CM	5-100w Incan. or 5-17w LED Med.	7¼"	5¾"	9¼" W, 4½" H

For flush mount options, see pages 24-26.

MERIDIAN™

FINISH CHROME
GLASS THICK FACETED
CLEAR INSIDE ETCHED

Meridian features minimal transitional styling with clean lines and low-profile faceted ½" thick glass. Overscaled barrel knob detailing completes this simplistic design.

Meridian Interior, pages 192-194

ADDITIONAL FINISHES

Brushed Nickel (BN)



5592 CM
5592 CM-LED
14" W, 6" H



3871 CM
16" DIA., 12¼" H



5590 CM
5590 CM-LED
5" W, 8" H



5593 CM
5593 CM-LED
21" W, 6" H



5594 CM
5594 CM-LED
29" W, 6" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY
3871 CM	3-60w G9*					5½" Dia. Canopy
5590 CM	1-60w G9*	5590 CM-LED	1-4.5w G9 LED**	6½"	4"	4½" W, 8" H Back Plate
5592 CM	2-60w G9*	5592 CM-LED	2-4.5w G9 LED**	6¼"	3¾"	8" W, 4½" H Back Plate
5593 CM	3-60w G9*	5593 CM-LED	3-4.5w G9 LED**	6¼"	3¾"	8" W, 4½" H Back Plate
5594 CM	4-60w G9*	5594 CM-LED	4-4.5w G9 LED**	6¼"	3¾"	8" W, 4½" H Back Plate

*G9 bulbs included. **G9 LED bulbs included. For complete product details and LED specifications, refer to hinkleylighting.com.

Meridian features minimal transitional styling with clean lines and low-profile faceted 1/2" thick glass. Overscaled barrel knob detailing completes this simplistic design.
Meridian Interior, pages 192-194

FINISH BRUSHED NICKEL
GLASS THICK FACETED
CLEAR INSIDE ETCHED

MERIDIAN™

ADDITIONAL FINISHES
Chrome (CM)



3871 BN
16" Dia., 12 1/4" H



5592 BN
5592 BN-LED
14" W, 6" H



5593 BN
5593 BN-LED
21" W, 6" H



5590 BN
5590 BN-LED
5" W, 8" H



5594 BN
5594 BN-LED
29" W, 6" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY
3871 BN	3-60w G9*					5 1/2" Dia. Canopy
5590 BN	1-60w G9*	5590 BN-LED	1-4.5w G9 LED**	6 1/2"	4"	4 1/2" W, 8" H Back Plate
5592 BN	2-60w G9*	5592 BN-LED	2-4.5w G9 LED**	6 1/4"	3 3/4"	8" W, 4 1/2" H Back Plate
5593 BN	3-60w G9*	5593 BN-LED	3-4.5w G9 LED**	6 1/4"	3 3/4"	8" W, 4 1/2" H Back Plate
5594 BN	4-60w G9*	5594 BN-LED	4-4.5w G9 LED**	6 1/4"	3 3/4"	8" W, 4 1/2" H Back Plate

*G9 bulbs included. **G9 LED bulbs included. For complete product details and LED specifications, refer to hinkleylighting.com.

BENNETT™

FINISH POLISHED ANTIQUE NICKEL
GLASS CLEAR HOLOPHANE

Charming and graceful, Bennett's distinctive details set it apart. Petite arched arms and latches bring an artisan touch to its transitional design while the pressed holophane glass cups add a dash of vintage panache.

ADDITIONAL FINISHES

Polished Nickel (PN)



5350 PL
5¼" W, 9" H




5352 PL
16" W, 8¾" H



5353 PL
24¼" W, 8¾" H



5354 PL
31¾" W, 8¾" H



5357 PL
5¼" W, 7¾" H
40¾" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
5350 PL	1-100w Med.	6¾"	6½"	5" Dia. Back Plate		
5352 PL	2-100w Med.	6¾"	6¼"	7" W, 5" H Back Plate		
5353 PL	3-100w Med.	6¾"	6¼"	9" W, 5" H Back Plate		
5354 PL	4-100w Med.	6¾"	6¼"	9" W, 5" H Back Plate		
5357 PL	1-100w Med.			5½" Dia. Canopy	12'	1-6', 2-12'

*Maximum achievable height with stems included. Additional 12" stems available, 4312 PL. For flush mount options, see pages 24-26.

Charming and graceful, Bennett's distinctive details set it apart. Petite arched arms and latches bring an artisan touch to its transitional design while the pressed holophane glass cups add a dash of vintage panache.

FINISH POLISHED NICKEL
GLASS CLEAR HOLOPHANE

BENNETT™

ADDITIONAL FINISHES
Polished Antique Nickel (PL)



5357 PN
5¼" W, 7¾" H
40¾" MAX. H*



5352 PN
16" W, 8¾" H



5350 PN
5¼" W, 9" H



5353 PN
24¼" W, 8¾" H



5354 PN
31¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
5350 PN	1-100w Med.	6¾"	6½"	5" Dia. Back Plate		
5352 PN	2-100w Med.	6¾"	6¼"	7" W, 5" H Back Plate		
5353 PN	3-100w Med.	6¾"	6¼"	9" W, 5" H Back Plate		
5354 PN	4-100w Med.	6¾"	6¼"	9" W, 5" H Back Plate		
5357 PN	1-100w Med.			5½" Dia. Canopy	10'	1-6', 2-12'

*Maximum achievable height with stems included. Additional 12" stems available, 6037 PN. For flush mount options, see pages 24-26.

BOYER™

FINISH OIL RUBBED BRONZE
WITH BRUSHED BRONZE

Industrial and polished, Boyer's charming mid-century modern style will add an element of history to any space. Two-tone finishes and contrasting reflectors are an ideal match with vintage filament bulbs for timeless style with a twist.

Boyer Interior, pages 140-143

ADDITIONAL FINISHES


Polished Nickel (PN)



5260 OZ
7" W, 9" H



5262 OZ
7" W, 18" H
(mounted vertically)



5262 OZ
18" W, 7" H



5263 OZ
26¾" W, 9" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5260 OZ	1-100w Med.	5½"	3½"	6" Dia.
5262 OZ	2-100w Med.	5¼"	3½"	6" Dia.
5263 OZ	3-100w Med.	5½"	3½"	6" Dia.

Ideal for vintage filament bulbs (not included). For flush mount options, see pages 24-26.

Industrial and polished, Boyer's charming mid-century modern style will add an element of history to any space. Two-tone finishes and contrasting reflectors are an ideal match with vintage filament bulbs for timeless style with a twist.

Boyer Interior, pages 140-143

FINISH POLISHED NICKEL
WITH ANTIQUE NICKEL

BOYER™

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



5262 PN
7" W, 18" H
(mounted vertically)



5260 PN
7" W, 9" H



5262 PN
18" W, 7" H



5263 PN
26¾" W, 9" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5260 PN	1-100w Med.	5½"	3½"	6" Dia.
5262 PN	2-100w Med.	5¼"	3½"	6" Dia.
5263 PN	3-100w Med.	5½"	3½"	6" Dia.

Ideal for vintage filament bulbs (not included). For flush mount options, see pages 24-26.

JACKSON™

FINISH POLISHED NICKEL
GLASS CLEAR SEEDY

Jackson merges traditional details such as clear seedy glass, finished glass collars and distinctive hammered accent plates to create a seamless, polished look that is at home in a rustic lodge or an urban loft.

ADDITIONAL FINISHES

Brushed Nickel (BN), Buckeye Bronze (KZ)



51823 PN
24" W, 7¼" H



51822 PN
16¼" W, 7¼" H



51820 PN
5" W, 7¼" H



51824 PN
32¾" W, 7¼" H



51825 PN
38¼" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
51820 PN	1-100w Med.	7"	¼"	5" W, 6¾" H	•
51822 PN	2-100w Med.	7"	5"	16¼" W, 5" H	•
51823 PN	3-100w Med.	7"	5"	24" W, 5" H	•
51824 PN	4-100w Med.	7"	5"	32¾" W, 5" H	•
51825 PN	5-100w Med.	7"	5"	38¼" W, 5" H	•

For flush mount options, see pages 24-26.

Jackson merges traditional details such as clear seeded glass, finished glass collars and distinctive hammered accent plates to create a seamless, polished look that is at home in a rustic lodge or an urban loft.

FINISH BUCKEYE BRONZE
WITH ANTIQUE COPPER
GLASS CLEAR SEEDY

JACKSON™

ADDITIONAL FINISHES
Brushed Nickel (BN), Polished Nickel (PN)



51822 KZ
16¼" W, 7¼" H



51823 KZ
24" W, 7¼" H



51824 KZ
32¾" W, 7¼" H



51820 KZ
5" W, 7¼" H



51825 KZ
38¼" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
51820 KZ	1-100w Med.	7"	4¼"	5" W, 6¾" H	•
51822 KZ	2-100w Med.	7"	5"	16¼" W, 5" H	•
51823 KZ	3-100w Med.	7"	5"	24" W, 5" H	•
51824 KZ	4-100w Med.	7"	5"	32¾" W, 5" H	•
51825 KZ	5-100w Med.	7"	5"	38¼" W, 5" H	•

For flush mount options, see pages 24-26.

JACKSON™

FINISH BRUSHED NICKEL
WITH POLISHED ANTIQUE NICKEL
GLASS CLEAR SEEDY

Jackson merges traditional details such as clear seedy glass, finished glass collars and distinctive hammered accent plates to create a seamless, polished look that is at home in a rustic lodge or an urban loft.

ADDITIONAL FINISHES

Buckeye Bronze (KZ), Polished Nickel (PN)



51823 BN
24" W, 7¼" H



51822 BN
16¼" W, 7¼" H



51820 BN
5" W, 7¼" H



51824 BN
32¾" W, 7¼" H



51825 BN
38¼" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
51820 BN	1-100w Med.	7"	4¼"	5" W, 6¾" H	•
51822 BN	2-100w Med.	7"	5"	16¼" W, 5" H	•
51823 BN	3-100w Med.	7"	5"	24" W, 5" H	•
51824 BN	4-100w Med.	7"	5"	32¾" W, 5" H	•
51825 BN	5-100w Med.	7"	5"	38¼" W, 5" H	•

For flush mount options, see pages 24-26.

Clancy is an updated traditional silhouette. Petite etched opal glass and a Brushed Nickel finish convey an understated elegance. Soft curves are echoed throughout the design, adding a vintage touch.
Clancy Interior, pages 74-77

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

CLANCY™



5442 BN
16" W, 8¼" H



3233 BN
16½" DIA., 5¾" H



5443 BN
25" W, 8¼" H



5440 BN
6" W, 11¼" H



5444 BN
32¾" W, 8¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5440 BN	1-100w Incan. or 1-17w LED Med.	6½"	6¼"	5" Dia.
5442 BN	2-100w Incan. or 2-17w LED Med.	6½"	5"	7" W, 5" H
5443 BN	3-100w Incan. or 3-17w LED Med.	6½"	5"	9" W, 5" H
5444 BN	4-100w Incan. or 4-17w LED Med.	6½"	5"	9" W, 5" H
3233 BN*	3-60w Med.			


*Recommended companion flush mount. For additional options, see pages 24-26.

CONGRESS™

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR, ETCHED OPAL

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials, and is the perfect vintage accent to any décor. Congress Interior, pages 91-103

1 CHOOSE A STYLE 2 CHOOSE A FINISH 3 CHOOSE A GLASS



50027 AN
50027 CM
50027 OZ (shown)
19¼" W, 12" H



50025 AN (shown)
50025 CM
50025 OZ
20" W, 11½" H



3173 AN
3173 CM (shown)
3173 OZ
7" W, 13½" H



50036 AN
50036 CM
50036 OZ (shown)
29½" W, 9¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
3173 AN, CM, OZ	1-100w Med.	9¼"	4¾"	4¾" Dia.	
50025 AN, CM, OZ	2-100w Med.	9¼"	3½"	4¾" Dia.	•
50027 AN, CM, OZ	2-100w Med.	9¾"	3½"	4¾" Dia.	•
50036 AN, CM, OZ	3-100w Med.	9¾"	3½"	4¾" Dia.	•

Ideal for vintage filament bulbs (not included). For flush mount options, see pages 24-26.

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials, and is the perfect vintage accent to any décor.
Congress Interior, pages 91-103

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
GLASS CLEAR SEEDY

CONGRESS™



50123 AN
50123 CM (shown)
50123 OZ
29½" W, 11¼" H



31700 AN
31700 CM
31700 OZ (shown)
6½" W, 13¼" H



50122 AN
50122 CM
50122 OZ (shown)
19" W, 11¼" H



50122 AN (shown)
50122 CM
50122 OZ
19" W, 11¼" H



31700 AN (shown)
31700 CM
31700 OZ
6½" W, 13¼" H



50123 AN
50123 CM
50123 OZ (shown)
29½" W, 11¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
31700 AN, CM, OZ	1-100w Med.	9"	4¾"	4¾" Dia.	
50122 AN, CM, OZ	2-100w Med.	9"	3½"	4¾" Dia.	•
50123 AN, CM, OZ	3-100w Med.	9"	3½"	4¾" Dia.	•

Ideal for vintage filament bulbs (not included). For flush mount options, see pages 24-26.

CONGRESS ORDERING GUIDE




SCONCES, 2 LIGHT & 3 LIGHT BATH

Outfit your space in retro-chic style!




Use the chart below to determine item numbers and specs for each Congress Bath fixture with clear, etched opal or clear seeded glass in three finish options.

<p>1 choose a style</p> <p>2 choose a finish</p> <p>3 choose a glass</p>	FINISH	CLEAR				ETCHED OPAL			CLEAR SEEDY
		Teardrop	Globe	Hurricane	Retro	Globe	Hurricane	Retro	Cylinder
									




SINGLE LIGHT SCONCE

	Antique Nickel	3177 AN 6" W 14" H	3174 AN 7" W 13½" H	3171 AN 8¾" W 13" H	3176 AN 8" W 11¼" H	3173 AN 7" W 13½" H	3175 AN 8¾" W 13" H	3170 AN 8" W 11¼" H	31700 AN 6½" W 13¼" H
	Chrome	3177 CM 6" W 14" H	3174 CM 7" W 13½" H	3171 CM 8¾" W 13" H	3176 CM 8" W 11¼" H	3173 CM 7" W 13½" H	3175 CM 8¾" W 13" H	3170 CM 8" W 11¼" H	31700 CM 6½" W 13¼" H
	Oil Rubbed Bronze	3177 OZ 6" W 14" H	3174 OZ 7" W 13½" H	3171 OZ 8¾" W 13" H	3176 OZ 8" W 11¼" H	3173 OZ 7" W 13½" H	3175 OZ 8¾" W 13" H	3170 OZ 8" W 11¼" H	31700 OZ 6½" W 13¼" H

TWO LIGHT BAR

	Antique Nickel	50027 AN 19¼" W 12" H	50024 AN 19¼" W 11½" H	50021 AN 20" W 11" H	50026 AN 19¼" W 9¼" H	50023 AN 19¼" W 11½" H	50025 AN 20" W 11" H	50020 AN 19¼" W 9¼" H	50122 AN 19" W 11¼" H
	Chrome	50027 CM 19¼" W 12" H	50024 CM 19¼" W 11½" H	50021 CM 20" W 11" H	50026 CM 19¼" W 9¼" H	50023 CM 19¼" W 11½" H	50025 CM 20" W 11" H	50020 CM 19¼" W 9¼" H	50122 CM 19" W 11¼" H
	Oil Rubbed Bronze	50027 OZ 19¼" W 12" H	50024 OZ 19¼" W 11½" H	50021 OZ 20" W 11" H	50026 OZ 19¼" W 9¼" H	50023 OZ 19¼" W 11½" H	50025 OZ 20" W 11" H	50020 OZ 19¼" W 9¼" H	50122 OZ 19" W 11¼" H

THREE LIGHT BAR

	Antique Nickel	50037 AN 29½" W 12" H	50034 AN 29½" W 11½" H	50031 AN 30" W 11" H	50036 AN 29½" W 9¼" H	50033 AN 29½" W 11½" H	50035 AN 30" W 11" H	50030 AN 29½" W 9¼" H	50123 AN 29½" W 11¼" H
	Chrome	50037 CM 29½" W 12" H	50034 CM 29½" W 11½" H	50031 CM 30" W 11" H	50036 CM 29½" W 9¼" H	50033 CM 29½" W 11½" H	50035 CM 30" W 11" H	50030 CM 29½" W 9¼" H	50123 CM 29½" W 11¼" H
	Oil Rubbed Bronze	50037 OZ 29½" W 12" H	50034 OZ 29½" W 11½" H	50031 OZ 30" W 11" H	50036 OZ 29½" W 9¼" H	50033 OZ 29½" W 11½" H	50035 OZ 30" W 11" H	50030 OZ 29½" W 9¼" H	50123 OZ 29½" W 11¼" H

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials, and is the perfect vintage accent to any décor.
Congress Interior, pages 91-103

FINISH ANTIQUE NICKEL,
CHROME, OIL RUBBED BRONZE
SHADE METAL

CONGRESS™



50038 AN (shown)
50038 CM
50038 OZ
31" W, 10½" H



3178 AN (shown)
3178 CM
3178 OZ
9¾" W, 12¾" H



50038 AN
50038 CM (shown)
50038 OZ
31" W, 10½" H



50028 AN
50028 CM (shown)
50028 OZ
21" W, 10½" H



50028 AN
50028 CM
50028 OZ (shown)
21" W, 10½" H



3178 AN
3178 CM
3178 OZ (shown)
9¾" W, 12¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
3178 AN, CM, OZ	1-100w Incan. or 1-17w LED Med.	10½"	4¾"	4¾" Dia.	
50028 AN, CM, OZ	2-100w Incan. or 2-17w LED Med.	10¾"	3½"	4¾" Dia.	•
50038 AN, CM, OZ	3-100w Incan. or 3-17w LED Med.	10¾"	3½"	4¾" Dia.	•

For flush mount options, see pages 24-26.

RIGBY™

FINISH ANTIQUE NICKEL
WITH HERITAGE BRASS
SHADE MESH

Rigby is inspired by the Americana barn light reborn as a chic interior retro classic. Features such as cast socket covers, mesh shades, canopy detail and two-tone finish options combine the best in both vintage and industrial design elements.

Rigby Interior, pages 106-109

ADDITIONAL FINISHES

Polished Nickel (PN)



5290 AN
8" W, 8¾" H



5292 AN
19" W, 8¾" H



5293 AN
27" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5290 AN	1-100w Med.	8¾"	2½"	5" Dia.
5292 AN	2-100w Med.	8¾"	3"	6" Dia.
5293 AN	3-100w Med.	8¾"	3"	6" Dia.

Ideal for vintage filament bulbs (not included). For flush mount options, see pages 24-26.

Rigby is inspired by the Americana barn light reborn as a chic interior retro classic. Features such as cast socket covers, mesh shades, canopy detail and two-tone finish options combine the best in both vintage and industrial design elements.

Rigby Interior, pages 106-109

FINISH POLISHED NICKEL
SHADE MESH

RIGBY™

ADDITIONAL FINISHES
Antique Nickel with Heritage Brass (AN)



5292 PN
19" W, 8¾" H



5290 PN
8" W, 8¾" H



5293 PN
27" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5290 PN	1-100w Med.	8¾"	2½"	5" Dia.
5292 PN	2-100w Med.	8¾"	3"	6" Dia.
5293 PN	3-100w Med.	8¾"	3"	6" Dia.

Ideal for vintage filament bulbs (not included). For flush mount options, see pages 24-26.

AINSLEY™

FINISH BUCKEYE BRONZE
GLASS CASÉD OPAL

Ainsley's traditional silhouette charms with distinctive details like retro-modern turned cups. Caséd opal glass shades are accented with an elegant Buckeye Bronze trim ring.

ADDITIONAL FINISHES

Brushed Nickel (BN), Polished Nickel (PN)



56552 KZ
16" W, 9¼" H



56553 KZ
24" W, 9¼" H



56550 KZ
6¼" W, 7½" H



56554 KZ
33" W, 9¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
56550 KZ	1-100w Incan. or 1-17w LED Med.	8¼"	4"	6" Dia.
56552 KZ	2-100w Incan. or 2-17w LED Med.	8¼"	5"	6" Dia.
56553 KZ	3-100w Incan. or 3-17w LED Med.	8¼"	5"	6" Dia.
56554 KZ	4-100w Incan. or 4-17w LED Med.	8¼"	5"	6" Dia.

For flush mount options, see pages 24-26.

Ainsley's traditional silhouette charms with distinctive details like retro-modern turned cups. Cased opal glass shades are accented with an elegant Brushed Nickel trim ring.

FINISH BRUSHED NICKEL
GLASS CASED OPAL

AINSLEY™

ADDITIONAL FINISHES
Buckeye Bronze (KZ), Polished Nickel (PN)



56552 BN
16" W, 9¼" H



3233 BN
16½" DIA., 5¾" H



56550 BN
6¼" W, 7½" H



56553 BN
24" W, 9¼" H



56554 BN
33" W, 9¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
56550 BN	1-100w Incan. or 1-17w LED Med.	8¼"	4"	6" Dia.
56552 BN	2-100w Incan. or 2-17w LED Med.	8¼"	5"	6" Dia.
56553 BN	3-100w Incan. or 3-17w LED Med.	8¼"	5"	6" Dia.
56554 BN	4-100w Incan. or 4-17w LED Med.	8¼"	5"	6" Dia.
3233 BN*	3-60w Med.			

*Recommended companion flush mount. For additional options, see pages 24-26.

AINSLEY™

FINISH POLISHED NICKEL
GLASS CASÉD OPAL

Ainsley's traditional silhouette charms with distinctive details like retro-modern turned cups. Caséd opal glass shades are accented with an elegant Polished Nickel trim ring.

ADDITIONAL FINISHES

Brushed Nickel (BN), Buckeye Bronze (KZ)



56552 PN
16" W, 9¼" H



56553 PN
24" W, 9¼" H



56550 PN
6¼" W, 7½" H



56554 PN
33" W, 9¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
56550 PN	1-100w Incan. or 1-17w LED Med.	8¼"	4"	6" Dia.
56552 PN	2-100w Incan. or 2-17w LED Med.	8¼"	5"	6" Dia.
56553 PN	3-100w Incan. or 3-17w LED Med.	8¼"	5"	6" Dia.
56554 PN	4-100w Incan. or 4-17w LED Med.	8¼"	5"	6" Dia.

For flush mount options, see pages 24-26.

Faye is a fresh take on traditional design with clean lines reinforcing a timeless sophistication. Softly curved cased opal glass cups, accented with step details, pair with a crisp Chrome finish for sparkling allure.

FINISH CHROME
GLASS CASÉD OPAL

FAYE™



5602 CM
15" W, 8¾" H



5551 CM
15" DIA., 7¾" H



5603 CM
24" W, 8¾" H



5600 CM
5¾" W, 8¾" H



5604 CM
33¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5600 CM	1-100w Incan. or 1-17w LED Med.	6¾"	5¼"	4¾" W, 4¾" H
5602 CM	2-100w Incan. or 2-17w LED Med.	6¾"	5¼"	7¼" W, 4¾" H
5603 CM	3-100w Incan. or 3-17w LED Med.	6¾"	5¼"	7¼" W, 4¾" H
5604 CM	4-100w Incan. or 4-17w LED Med.	6¾"	5¼"	7¼" W, 4¾" H
5551 CM*	2-60w Med.			

*Recommended companion flush mount. For additional options, see pages 24-26.

ASHLEY™

FINISH CHROME
GLASS ETCHED OPAL; STEPPED TRIM DETAIL

Ashley's chic, transitional style highlights its distinctive cast perforated glass holders and stepped trim detail in a crisp Chrome finish.



5192 CM
12¾" W, 7¼" H



5191 CM
15¾" DIA., 7" H



5193 CM
19¼" W, 7¼" H



5190 CM
5" W, 8½" H



5194 CM
26¾" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5190 CM	1-100w Incan. or 1-17w LED Med.	6¼"	4¼"	5" W, 8½" H
5191 CM	3-60w Med.			
5192 CM	2-100w Incan. or 2-17w LED Med.	6¼"	4¾"	8½" W, 5" H
5193 CM	3-100w Incan. or 3-17w LED Med.	6¼"	4¾"	8½" W, 5" H
5194 CM	4-100w Incan. or 4-17w LED Med.	6¼"	4¾"	8½" W, 5" H

Josie's delicate transitional style features a one inch rectangular wave element as the centerpiece of the design, along with etched opal glass that transitions from round on the bottom to square on the top. The Brushed Nickel finish and invis-mount raceway back plate add to its clean look.

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

JOSIE™



5551 BN
15" DIA., 7¾"



5372 BN
15½" W, 7¼" H



5370 BN
4½" W, 8½" H



5373 BN
23" W, 8" H



5375 BN
37½" W, 8½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5370 BN	1-100w Incan. or 1-17w LED Med.	6¼"	5"	4½" W, 7¼" H	•
5372 BN	2-100w Incan. or 2-17w LED Med.	6"	5"	7¼" W, 4½" H	•
5373 BN	3-100w Incan. or 3-17w LED Med.	6"	5¾"	18" W, 4½" H	•
5375 BN	5-100w Incan. or 5-17w LED Med.	6"	6¼"	18" W, 4½" H	
5551 BN*	2-60w Med.				

*Recommended companion flush mount. For additional options, see pages 24-26.

BOLLA™

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

The graceful lines of Bolla create a soft elegance, while heavy cast ball transition detail add to its innovative style. The strong proportions of the design contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Interior, pages 202-219

ADDITIONAL FINISHES

Brushed Nickel with Clear Seedy glass (BN-CL), Olde Bronze (OB),
Olde Bronze with Clear Seedy glass (OB-CL), Olde Bronze with Opal glass (OB-OPAL)



4660 BN
4660 BN-LED
16¾" W, 8" H



5893 BN
26" W, 8¾" H



5894 BN
35¾" W, 8¾" H



5892 BN
16" W, 8¾" H



4650 BN
7¾" W, 8½" H



5895 BN
45¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
4650 BN	1-100w Incan. or 1-17w LED Med.							8¾"	3½"	6" W, 7½" H Back Plate
4660 BN	2-75w Med.	4660 BN-LED	32w LED	1900	2700K	96	2-75w			5" Dia. Canopy
5892 BN	2-100w Incan. or 2-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5893 BN	3-100w Incan. or 3-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5894 BN	4-100w Incan. or 4-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5895 BN	5-100w Incan. or 5-17w LED Med.							6¾"	6½"	18¼" W, 4½" H Back Plate

For complete product details and LED specifications, refer to hinkleylighting.com.

The graceful lines of Bolla create a soft elegance, while heavy cast ball transition detail add to its innovative style. The strong proportions of the design contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Interior, pages 202-219

FINISH BRUSHED NICKEL
GLASS CLEAR SEEDY

BOLLA™

ADDITIONAL FINISHES

Brushed Nickel (BN), Olde Bronze (OB), Olde Bronze with Clear Seedy glass (OB-CL), Olde Bronze with Opal glass (OB-OPAL)



5893 BN-CL
26" W, 8¾" H



4650 BN-CL
7¾" W, 8½" H



5892 BN-CL
16" W, 8¾" H



5894 BN-CL
35¾" W, 8¾" H



5895 BN-CL
45¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
4650 BN-CL	1-100w Med.	8¾"	3½"	6" W, 7½" H
5892 BN-CL	2-100w Med.	6¾"	6½"	9¼" W, 4½" H
5893 BN-CL	3-100w Med.	6¾"	6½"	9¼" W, 4½" H
5894 BN-CL	4-100w Med.	6¾"	6½"	9¼" W, 4½" H
5895 BN-CL	5-100w Med.	6¾"	6½"	18¼" W, 4½" H

For flush mount options, see pages 24-26.

BOLLA™

FINISH OLDE BRONZE
GLASS ETCHED OPAL

The graceful lines of Bolla create a soft elegance, while heavy cast ball transition detail add to its innovative style. The strong proportions of the design contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Interior, pages 202-219

ADDITIONAL FINISHES

Brushed Nickel (BN), Brushed Nickel with Clear Seedy glass (BN-CL),
Olde Bronze (OB), Olde Bronze with Clear Seedy glass (OB-CL)



4660 OB-OPAL
4660 OB-OP-LED
16¾" W, 8" H



5893 OB-OPAL
26" W, 8¾" H



5894 OB-OPAL
35¾" W, 8¾" H



5892 OB-OPAL
16" W, 8¾" H



4650 OB-OPAL
7¾" W, 8½" H



5895 OB-OPAL
45¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
4650 OB-OPAL	1-100w Incan. or 1-17w LED Med.							8¾"	3½"	6" W, 7½" H Back Plate
4660 OB-OPAL	2-75w Med.	4660 OB-OP-LED	32w LED	1900	2700K	96	2-75w			5" Dia. Canopy
5892 OB-OPAL	2-100w Incan. or 2-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5893 OB-OPAL	3-100w Incan. or 3-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5894 OB-OPAL	4-100w Incan. or 4-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5895 OB-OPAL	5-100w Incan. or 5-17w LED Med.							6¾"	6½"	18¼" W, 4½" H Back Plate

For complete product details and LED specifications, refer to hinkleylighting.com.

The graceful lines of Bolla create a soft elegance, while heavy cast ball transition detail add to its innovative style. The strong proportions of the design contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Interior, pages 202-219

FINISH OLDE BRONZE
GLASS CLEAR SEEDY

BOLLA™

ADDITIONAL FINISHES
Brushed Nickel (BN), Brushed Nickel with Clear Seedy glass (BN-CL),
Olde Bronze (OB), Olde Bronze with Opal glass (OB-OPAL)



5893 OB-CL
26" W, 8¾" H



4660 OB-CL
16¾" W, 8" H



5892 OB-CL
16" W, 8¾" H



5894 OB-CL
35¾" W, 8¾" H



5895 OB-CL
45¾" W, 8¾" H



4650 OB-CL
7¾" W, 8½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY
4650 OB-CL	1-100w Med.	8¾"	3½"	6" W, 7½" H Back Plate
4660 OB-CL	2-75w Med.			5" Dia. Canopy
5892 OB-CL	2-100w Med.	6¾"	6½"	9¼" W, 4½" H Back Plate
5893 OB-CL	3-100w Med.	6¾"	6½"	9¼" W, 4½" H Back Plate
5894 OB-CL	4-100w Med.	6¾"	6½"	9¼" W, 4½" H Back Plate
5895 OB-CL	5-100w Med.	6¾"	6½"	18¼" W, 4½" H Back Plate

BOLLA™

FINISH OLDE BRONZE
GLASS LIGHT AMBER SEEDY

The graceful lines of Bolla create a soft elegance, while heavy cast ball transition detail add to its innovative style. The strong proportions of the design contrast with the subtle bell shaped glass, combining both traditional and modern details.

Bolla Interior, pages 202-219

ADDITIONAL FINISHES

Brushed Nickel (BN), Brushed Nickel with Clear Seedy glass (BN-CL),
Olde Bronze with Clear Seedy glass (OB-CL), Olde Bronze with Opal glass (OB-OPAL)



4660 OB
4660 OB-LED
16¾" W, 8" H



5893 OB
26" W, 8¾" H



5894 OB
35¾" W, 8¾" H



5892 OB
16" W, 8¾" H



4650 OB
7¾" W, 8½" H



5895 OB
45¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
4650 OB	1-100w Incan. or 1-17w LED Med.							8¾"	3½"	6" W, 7½" H Back Plate
4660 OB	2-75w Med.	4660 OB-LED	32w LED	1900	2700K	96	2-75w			5" Dia. Canopy
5892 OB	2-100w Incan. or 2-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5893 OB	3-100w Incan. or 3-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5894 OB	4-100w Incan. or 4-17w LED Med.							6¾"	6½"	9¼" W, 4½" H Back Plate
5895 OB	5-100w Incan. or 5-17w LED Med.							6¾"	6½"	18¼" W, 4½" H Back Plate

For complete product details and LED specifications, refer to hinkleylighting.com.



JILL SHARP WEEKS
JILL SHARP STUDIO
CHARLESTON, SC

"I mix un-lacquered brass with oil rubbed bronze and black very fluidly. Hardware on doors and cabinets and trims on faucets and lighting fixtures finishes should not be the same—it's about creating a beautiful balance, not being matchy."

ABOVE: THE ALICE COLLECTION | 5832BR, PAGE 392

ALICE™

FINISH BRUSHED BRONZE
GLASS ETCHED OPAL

Alice's classic design features decorative half round turnings and coordinating cast end caps. Available in Antique Nickel and Brushed Bronze finishes to complement the elegant etched opal glass, this style will add beauty to any décor.

ADDITIONAL FINISHES

Antique Nickel (AN)



5551 BR
15" DIA., 7¾" H



5832 BR
17" W, 8" H



5830 BR
5¼" W, 8¾" H



5833 BR
27" W, 8" H



5834 BR
36¾" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5551 BR*	2-60w Med.				
5830 BR	1-100w Incan. or 1-17w LED Med.	7½"	4"	5¼" W, 8" H	•
5832 BR	2-100w Incan. or 2-17w LED Med.	7½"	3¼"	8" W, 5¼" H	•
5833 BR	3-100w Incan. or 3-17w LED Med.	7½"	3¼"	8" W, 5¼" H	•
5834 BR	4-100w Incan. or 4-17w LED Med.	7½"	3¼"	8" W, 5¼" H	•

*Recommended companion flush mount. For additional options, see pages 24-26.

Alice's classic design features decorative half round turnings and coordinating cast end caps. Available in Antique Nickel and Brushed Bronze finishes to complement the elegant etched opal glass, this style will add beauty to any décor.

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL

ALICE™

ADDITIONAL FINISHES
Brushed Bronze (BR)



5832 AN
17" W, 8" H



5551 BN
15" DIA., 7¾" H



5833 AN
27" W, 8" H



5830 AN
5¼" W, 8¾" H



5834 AN
36¾" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5551 BN*	2-60w Med.				
5830 AN	1-100w Incan. or 1-17w LED Med.	7½"	4"	5¼" W, 8" H	•
5832 AN	2-100w Incan. or 2-17w LED Med.	7½"	¾"	8" W, 5¼" H	•
5833 AN	3-100w Incan. or 3-17w LED Med.	7½"	¾"	8" W, 5¼" H	•
5834 AN	4-100w Incan. or 4-17w LED Med.	7½"	¾"	8" W, 5¼" H	•

*Recommended companion flush mount. For additional options, see pages 24-26.

BALDWIN™

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL

Inspired by classic drawer pulls, Baldwin perfectly fuses transitional and traditional style elements. A precision die-cast back plate, knob and glass fitter complement the tapered square etched opal glass shades for a silhouette that adds beauty to any décor.

ADDITIONAL FINISHES

Polished Nickel (PN)



56672 AN
13¾" W, 7" H



56673 AN
23½" W, 7" H



56670 AN
4½" W, 8¼" H



56674 AN
33½" W, 7" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
56670 AN	1-100w Incan. or 1-17w LED Med.	5½"	3¾"	4½" W, 7½" H	•
56672 AN	2-100w Incan. or 2-17w LED Med.	6"	3¾"	7½" W, 4½" H	•
56673 AN	3-100w Incan. or 3-17w LED Med.	6"	3¾"	7½" W, 4½" H	•
56674 AN	4-100w Incan. or 4-17w LED Med.	6"	3¾"	7½" W, 4½" H	•

For flush mount options, see pages 24-26.

Inspired by classic drawer pulls, Baldwin perfectly fuses transitional and traditional style elements. A precision die-cast back plate, knob and glass fitter complement the tapered square etched opal glass shades for a silhouette that adds beauty to any décor.

FINISH POLISHED NICKEL
GLASS ETCHED OPAL

BALDWIN™

ADDITIONAL FINISHES
Antique Nickel (AN)



56672 PN
13¾" W, 7" H



56670 PN
4½" W, 8¼" H



56673 PN
23½" W, 7" H



56674 PN
33½" W, 7" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
56670 PN	1-100w Incan. or 1-17w LED Med.	5½"	3¾"	4½" W, 7½" H	•
56672 PN	2-100w Incan. or 2-17w LED Med.	6"	3¾"	7½" W, 4½" H	•
56673 PN	3-100w Incan. or 3-17w LED Med.	6"	3¾"	7½" W, 4½" H	•
56674 PN	4-100w Incan. or 4-17w LED Med.	6"	3¾"	7½" W, 4½" H	•

For flush mount options, see pages 24-26.

SADIE™

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

Sadie's transitional design showcases an elegantly arched cross bar. Slim and graceful, the etched opal glass can be mounted either up or down for maximum flexibility and the Brushed Nickel finish ensures Sadie is the perfect complement to any spa setting.



5421 BN
17" DIA., 7" H



52232 BN
15¾" W, 8¾" H



52233 BN
23¼" W, 8¾" H



52230 BN
5¾" W, 7¾" H



52234 BN
32¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
52230 BN	1-100w Incan. or 1-17w LED Med.	7"	3½"	5¾" Dia.
52232 BN	2-100w Incan. or 2-17w LED Med.	7¾"	6"	5¾" Dia.
52233 BN	3-100w Incan. or 3-17w LED Med.	8"	6"	5¾" Dia.
52234 BN	4-100w Incan. or 4-17w LED Med.	8¼"	6"	5¾" Dia.
5421 BN*	3-60w Med.			

*Recommended companion flush mount. For additional options, see pages 24-26.

Darby's traditional flair will complement any décor with a precision die-cast zinc back plate, arm, cup and end caps in a flawless Brushed Caramel, Brushed Nickel or Polished Nickel finish. A thin reeded bar effortlessly balances tapered square etched opal shades for an alluring effect.

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

DARBY™

ADDITIONAL FINISHES
Brushed Caramel (BC), Polished Nickel (PN)



53012 BN
14" W, 8" H



5421 BN
17" DIA., 7" H



53010 BN
5¾" W, 8¼" H



53013 BN
23" W, 8" H



53014 BN
32" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
53010 BN	1-100w Incan. or 1-17w LED Med.	5"	6¾"	5¾" Square	•
53012 BN	2-100w Incan. or 2-17w LED Med.	5"	6¾"	7½" W, 5" H	•
53013 BN	3-100w Incan. or 3-17w LED Med.	5"	6¾"	7½" W, 5" H	•
53014 BN	4-100w Incan. or 4-17w LED Med.	5"	6¾"	7½" W, 5" H	•
5421 BN*	3-60w Med.				

*Recommended companion flush mount. For additional options, see pages 24-26.

DARBY™

FINISH POLISHED NICKEL
GLASS ETCHED OPAL

Darby's traditional flair will complement any décor with a precision die-cast zinc back plate, arm, cup and end caps in a flawless Brushed Caramel, Brushed Nickel or Polished Nickel finish. A thin reeded bar effortlessly balances tapered square etched opal shades for an alluring effect.

ADDITIONAL FINISHES

Brushed Caramel (BC), Brushed Nickel (BN)



53012 PN
14" W, 8" H



53013 PN
23" W, 8" H



53010 PN
5¾" W, 8¼" H



53014 PN
32" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
53010 PN	1-100w Incan. or 1-17w LED Med.	5"	6¾"	5¾" Square	•
53012 PN	2-100w Incan. or 2-17w LED Med.	5"	6¾"	7½" W, 5" H	•
53013 PN	3-100w Incan. or 3-17w LED Med.	5"	6¾"	7½" W, 5" H	•
53014 PN	4-100w Incan. or 4-17w LED Med.	5"	6¾"	7½" W, 5" H	•

For flush mount options, see pages 24-26.

Darby's traditional flair will complement any décor with a precision die-cast zinc back plate, arm, cup and end caps in a flawless Brushed Caramel, Brushed Nickel or Polished Nickel finish. A thin reeded bar effortlessly balances tapered square etched opal shades for an alluring effect.

FINISH BRUSHED CARAMEL
GLASS ETCHED OPAL

DARBY™

ADDITIONAL FINISHES
Brushed Nickel (BN), Polished Nickel (PN)



53012 BC
14" W, 8" H



53010 BC
5¾" W, 8¼" H



53013 BC
23" W, 8" H



53014 BC
32" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
53010 BC	1-100w Incan. or 1-17w LED Med.	5"	6¾"	5¾" Square	•
53012 BC	2-100w Incan. or 2-17w LED Med.	5"	6¾"	7½" W, 5" H	•
53013 BC	3-100w Incan. or 3-17w LED Med.	5"	6¾"	7½" W, 5" H	•
53014 BC	4-100w Incan. or 4-17w LED Med.	5"	6¾"	7½" W, 5" H	•

For flush mount options, see pages 24-26.

THISTLEDOWN™

FINISH POLISHED NICKEL
GLASS CLEAR SEEDY

Thistledown is an updated traditional design with smooth, flowing lines and a practical elegance that adds sophistication to any space.

ADDITIONAL FINISHES

Brushed Nickel (BN)



51802 PN
16" W, 10¼" H



51800 PN
5¼" W, 10½" H



51803 PN
24" W, 10½" H



51804 PN
30" W, 10¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
51800 PN	1-100w Med.	6¼"	7"	5" W, 7" H
51802 PN	2-100w Med.	6¼"	8"	7" W, 5" H
51803 PN	3-100w Med.	6¼"	8"	7" W, 5" H
51804 PN	4-100w Med.	6¼"	8"	9" W, 5" H

For flush mount options, see pages 24-26.

Thistledown is an updated traditional design with smooth, flowing lines and a practical elegance that adds sophistication to any space.

FINISH BRUSHED NICKEL
GLASS CLEAR SEEDY

THISTLEDOWN™

ADDITIONAL FINISHES
Polished Nickel (PN)



51802 BN-CL
16" W, 10¼" H



51803 BN-CL
24" W, 10½" H



51800 BN-CL
5¼" W, 10½" H



51804 BN-CL
30" W, 10¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
51800 BN-CL	1-100w Med.	6¼"	7"	5" W, 7" H
51802 BN-CL	2-100w Med.	6¼"	8"	7" W, 5" H
51803 BN-CL	3-100w Med.	6¼"	8"	7" W, 5" H
51804 BN-CL	4-100w Med.	6¼"	8"	9" W, 5" H

For flush mount options, see pages 24-26.

COLETTE™

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

Colette defines classic elegance. This traditional style features thick, pressed white etched glass paired with hand-lathed finials and transition detailing.

ADDITIONAL FINISHES

Chrome (CM), Oil Rubbed Bronze (OZ)



3782 AN
13¾" DIA., 5" H



58782 BN
17" W, 8" H



58783 BN
26¼" W, 8" H



58780 BN
6" W, 8½" H



58784 BN
33¼" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3782 AN*	2-40w Med.			
58780 BN	1-100w Incan. or 1-17w LED Med.	7½"	5"	4½" W, 7¼" H
58782 BN	2-100w Incan. or 2-17w LED Med.	7½"	5"	7¼" W, 4½" H
58783 BN	3-100w Incan. or 3-17w LED Med.	7½"	5"	9" W, 4½" H
58784 BN	4-100w Incan. or 4-17w LED Med.	7½"	5"	11½" W, 4½" H

*Recommended companion flush mount. For additional options, see pages 24-26.

Colette defines classic elegance. This traditional style features thick, pressed white etched glass paired with hand-lathed finials and transition detailing.

FINISH CHROME
GLASS ETCHED OPAL

COLETTE™

ADDITIONAL FINISHES
Brushed Nickel (BN), Oil Rubbed Bronze (OZ)



58782 CM
17" W, 8" H



58780 CM
6" W, 8½" H



58783 CM
26¼" W, 8" H



58784 CM
33¼" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
58780 CM	1-100w Incan. or 1-17w LED Med.	7½"	5"	4½" W, 7¼" H
58782 CM	2-100w Incan. or 2-17w LED Med.	7½"	5"	7¼" W, 4½" H
58783 CM	3-100w Incan. or 3-17w LED Med.	7½"	5"	9" W, 4½" H
58784 CM	4-100w Incan. or 4-17w LED Med.	7½"	5"	11½" W, 4½" H

For flush mount options, see pages 24-26.

COLETTE™

FINISH OIL RUBBED BRONZE
GLASS ETCHED OPAL

Colette defines classic elegance. This traditional style features thick, pressed white etched glass paired with hand-lathed finials and transition detailing.

ADDITIONAL FINISHES

Brushed Nickel (BN), Chrome (CM)



3782 OZ
13¾" DIA., 5" H



58782 OZ
17" W, 8" H



58783 OZ
26¼" W, 8" H



58780 OZ
6" W, 8½" H



58784 OZ
33¼" W, 8" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3782 OZ*	2-40w Med.			
58780 OZ	1-100w Incan. or 1-17w LED Med.	7½"	5"	4½" W, 7¼" H
58782 OZ	2-100w Incan. or 2-17w LED Med.	7½"	5"	7¼" W, 4½" H
58783 OZ	3-100w Incan. or 3-17w LED Med.	7½"	5"	9" W, 4½" H
58784 OZ	4-100w Incan. or 4-17w LED Med.	7½"	5"	11½" W, 4½" H

*Recommended companion flush mount. For additional options, see pages 24-26.

Abbie's elegant design features robust square tube construction enhanced by bold decorative cast finials. The six-sided glass shades are ribbed and flared, providing additional sophistication.

FINISH BRUSHED CARAMEL
GLASS ETCHED

ABBIE™

ADDITIONAL FINISHES
Brushed Nickel (BN), Chrome (CM)



5853 BC
25 1/4" W, 7 3/4" H



5850 BC
6 3/4" W, 7 3/4" H



5854 BC
34 1/2" W, 7 3/4" H



5852 BC
16" W, 7 3/4" H



5855 BC
43 3/4" W, 7 3/4" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5850 BC	1-100w Incan. or 1-17w LED Med.	7 1/2"	4 1/2"	4 1/2" W, 6 1/2" H
5852 BC	2-100w Incan. or 2-17w LED Med.	7 1/2"	5 1/4"	6 1/2" W, 4 1/2" H
5853 BC	3-100w Incan. or 3-17w LED Med.	7 1/2"	5 1/4"	6 1/2" W, 4 1/2" H
5854 BC	4-100w Incan. or 4-17w LED Med.	7 1/2"	5 1/4"	6 1/2" W, 4 1/2" H
5855 BC	5-100w Incan. or 5-17w LED Med.	7 1/2"	5 1/4"	6 1/2" W, 4 1/2" H

For flush mount options, see pages 24-26.

ABBIE™

FINISH BRUSHED NICKEL
GLASS ETCHED

Abbie's elegant design features robust square tube construction enhanced by bold decorative cast finials. The six-sided glass shades are ribbed and flared, providing additional sophistication.

ADDITIONAL FINISHES

Brushed Caramel (BC), Chrome (CM)



5850 BN
6¾" W, 7¾" H



5853 BN
25¼" W, 7¾" H



5852 BN
16" W, 7¾" H



5854 BN
34½" W, 7¾" H



5855 BN
43¾" W, 7¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5850 BN	1-100w Incan. or 1-17w LED Med.	7½"	4½"	4½" W, 6½" H
5852 BN	2-100w Incan. or 2-17w LED Med.	7½"	5¼"	6½" W, 4½" H
5853 BN	3-100w Incan. or 3-17w LED Med.	7½"	5¼"	6½" W, 4½" H
5854 BN	4-100w Incan. or 4-17w LED Med.	7½"	5¼"	6½" W, 4½" H
5855 BN	5-100w Incan. or 5-17w LED Med.	7½"	5¼"	6½" W, 4½" H

For flush mount options, see pages 24-26.

Abbie's elegant design features robust square tube construction enhanced by bold decorative cast finials. The six-sided glass shades are ribbed and flared, providing additional sophistication.

FINISH CHROME
GLASS ETCHED

ABBIE™

ADDITIONAL FINISHES
Brushed Caramel (BC), Brushed Nickel (BN)



5853 CM
25¼" W, 7¾" H



5850 CM
6¾" W, 7¾" H



5854 CM
34½" W, 7¾" H



5852 CM
16" W, 7¾" H



5855 CM
43¾" W, 7¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5850 CM	1-100w Incan. or 1-17w LED Med.	7½"	4½"	4½" W, 6½" H
5852 CM	2-100w Incan. or 2-17w LED Med.	7½"	5¼"	6½" W, 4½" H
5853 CM	3-100w Incan. or 3-17w LED Med.	7½"	5¼"	6½" W, 4½" H
5854 CM	4-100w Incan. or 4-17w LED Med.	7½"	5¼"	6½" W, 4½" H
5855 CM	5-100w Incan. or 5-17w LED Med.	7½"	5¼"	6½" W, 4½" H

For flush mount options, see pages 24-26.

YORKTOWN™

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL

The elegant Yorktown collection offers updated traditional styling with cast detailing for an authentic touch. The cast back plate, detailed finials, bar ends and transition balls combine to make this classic design perfect for any décor.

ADDITIONAL FINISHES

Brushed Bronze (BR)



5742 AN
15½" W, 9¾" H



5740 AN
4¾" W, 10" H



5743 AN
23¾" W, 9½" H



5744 AN
32¾" W, 9¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5740 AN	1-100w Incan. or 1-17w LED Med.	5¾"	5"	4½" W, 10" H
5742 AN	2-100w Incan. or 2-17w LED Med.	6¾"	7¼"	10" W, 4½" H
5743 AN	3-100w Incan. or 3-17w LED Med.	7¼"	7¼"	10" W, 4½" H
5744 AN	4-100w Incan. or 4-17w LED Med.	7"	7¼"	10" W, 4½" H

For flush mount options, see pages 24-26.

The elegant Yorktown collection offers updated traditional styling with cast detailing for an authentic touch. The cast back plate, detailed finials, bar ends and transition balls combine to make this classic design perfect for any décor.

FINISH BRUSHED BRONZE
GLASS ETCHED OPAL

YORKTOWN™

ADDITIONAL FINISHES
Antique Nickel (AN)



5742 BR
15½" W, 9¾" H



5743 BR
23¾" W, 9½" H



5740 BR
4¾" W, 10" H



5744 BR
32¾" W, 9¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5740 BR	1-100w Incan. or 1-17w LED Med.	5¾"	5"	4½" W, 10" H
5742 BR	2-100w Incan. or 2-17w LED Med.	6¾"	7¼"	10" W, 4½" H
5743 BR	3-100w Incan. or 3-17w LED Med.	7¼"	7¼"	10" W, 4½" H
5744 BR	4-100w Incan. or 4-17w LED Med.	7"	7¼"	10" W, 4½" H

For flush mount options, see pages 24-26.

SHELLY™

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

Shelly offers a sophisticated style statement with six-sided, etched opal fluted glass and decorative cast finials in either Brushed Nickel or Chrome finishes.

ADDITIONAL FINISHES

Chrome (CM)



5012 BN
16" W, 8½" H



5013 BN
24¼" W, 8½" H



5010 BN
5½" W, 9½" H



5014 BN
32¼" W, 8½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5010 BN	1-100w Incan. or 1-17w LED Med.	7½"	4½"	4¾" W, 9" H
5012 BN	2-100w Incan. or 2-17w LED Med.	7¾"	4¼"	9" W, 4¾" H
5013 BN	3-100w Incan. or 3-17w LED Med.	7¾"	4¼"	9" W, 4¾" H
5014 BN	4-100w Incan. or 4-17w LED Med.	7¾"	4¼"	9" W, 4¾" H

For flush mount options, see pages 24-26.

Shelly offers a sophisticated style statement with six-sided, etched opal fluted glass and decorative cast finials in either Brushed Nickel or Chrome finishes.

FINISH CHROME
GLASS ETCHED OPAL

SHELLY™

ADDITIONAL FINISHES
Brushed Nickel (BN)



5012 CM
16" W, 8½" H



5013 CM
24¼" W, 8½" H



5010 CM
5½" W, 9½" H



5014 CM
32¼" W, 8½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5010 CM	1-100w Incan. or 1-17w LED Med.	7½"	4½"	4¾" W, 9" H
5012 CM	2-100w Incan. or 2-17w LED Med.	7¾"	4¼"	9" W, 4¾" H
5013 CM	3-100w Incan. or 3-17w LED Med.	7¾"	4¼"	9" W, 4¾" H
5014 CM	4-100w Incan. or 4-17w LED Med.	7¾"	4¼"	9" W, 4¾" H

For flush mount options, see pages 24-26.

BLYTHE™

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL

Blythe sparkles with an air of refinement and elegance, with a precision die-cast back plate emphasizing quality. Faceted crystal knobs are precisely placed, subtly accenting each angle to enhance its chic, transitional style.

ADDITIONAL FINISHES

Polished Nickel (PN)



5282 AN
16" W, 9" H



5283 AN
25" W, 9" H



5820 AN
5" W, 9" H



5284 AN
34" W, 9" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5280 AN	1-100w Incan. or 1-17w LED Med.	6½"	5½"	5" Dia.	•
5282 AN	2-100w Incan. or 2-17w LED Med.	5¼"	5"	8" W, 5" H	•
5283 AN	3-100w Incan. or 3-17w LED Med.	5½"	5"	8" W, 5" H	•
5284 AN	4-100w Incan. or 4-17w LED Med.	5½"	5"	8" W, 5" H	•

For flush mount options, see pages 24-26.

Blythe sparkles with an air of refinement and elegance, with a precision die-cast back plate emphasizing quality. Faceted crystal knobs are precisely placed, subtly accenting each angle to enhance its chic, transitional style.

FINISH POLISHED NICKEL
GLASS ETCHED OPAL

BLYTHE™

ADDITIONAL FINISHES
Antique Nickel (AN)



5282 PN
16" W, 9" H



5820 PN
5" W, 9" H



5283 PN
25" W, 9" H



5284 PN
34" W, 9" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
5280 PN	1-100w Incan. or 1-17w LED Med.	6½"	5½"	5" Dia.	•
5282 PN	2-100w Incan. or 2-17w LED Med.	5¼"	5"	8" W, 5" H	•
5283 PN	3-100w Incan. or 3-17w LED Med.	5½"	5"	8" W, 5" H	•
5284 PN	4-100w Incan. or 4-17w LED Med.	5½"	5"	8" W, 5" H	•

For flush mount options, see pages 24-26.

BRANTLEY™

FINISH BRUSHED NICKEL
GLASS ETCHED OPAL

Brantley's transitional design features bold arms that sweep outward, creating a dramatic yet elegant effect. Its unique geometric castings and decorative arm construction add to its beauty, making this collection a perfect complement to any décor.

Brantley Interior, pages 220-223

ADDITIONAL FINISHES

Olde Bronze (OB)



4631 BN
17" DIA., 7" H



5362 BN
14½" W, 7¼" H



4630 BN
4¾" W, 12¼" H



5363 BN
24¼" W, 7¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
4630 BN	1-100w Incan. or 1-17w LED Med.	8½"	7"	4¾" W, 10" H
4631 BN	3-60w Med.			
5362 BN	2-100w Incan. or 2-17w LED Med.	8"	4½"	10" W, 4¾" H
5363 BN	3-100w Incan. or 3-17w LED Med.	8½"	4½"	10" W, 4¾" H

Brantley bath fixtures can be mounted facing up or down.

Brantley's transitional design features bold arms that sweep outward, creating a dramatic yet elegant effect.

Its unique geometric castings and decorative arm construction add to its beauty, making this collection a perfect complement to any décor.

Brantley Interior, pages 220-223

FINISH OLDE BRONZE
GLASS ETCHED OPAL

BRANTLEY™

ADDITIONAL FINISHES
Brushed Nickel (BN)



5362 OB
14½" W, 7¼" H



4631 OZ-WH
17" DIA., 7" H



5363 OB
24¼" W, 7¼" H



4630 OB
4¾" W, 12¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
4630 OB	1-100w Incan. or 1-17w LED Med.	8½"	7"	4¾" W, 10" H
4631 OZ-WH	3-60w Med.			
5362 OB	2-100w Incan. or 2-17w LED Med.	8"	4½"	10" W, 4¾" H
5363 OB	3-100w Incan. or 3-17w LED Med.	8½"	4½"	10" W, 4¾" H

Brantley bath fixtures can be mounted facing up or down.

BROOKE™

FINISH SILVER LEAF
GLASS ETCHED OPAL

Brooke's updated traditional look features a minimalist forged scroll design in Silver Leaf that elegantly complements its etched opal glass.

ADDITIONAL FINISHES

Antique Nickel (AN), Olde Bronze (OB)



5000 SL
5¼" W, 11¾" H



5003 SL
24" W, 10¾" H



5004 SL
31¼" W, 11" H



5002 SL
16½" W, 10¼" H



5005 SL
41½" W, 11" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5000 SL	1-100w Incan. or 1-17w LED Med.	5½"	8"	4½" W, 7¼" H
5002 SL	2-100w Incan. or 2-17w LED Med.	6¼"	6½"	9¼" W, 4½" H
5003 SL	3-100w Incan. or 3-17w LED Med.	6¼"	7¼"	9¼" W, 4½" H
5004 SL	4-100w Incan. or 4-17w LED Med.	6¼"	7"	9¼" W, 4½" H
5005 SL	5-100w Incan. or 5-17w LED Med.	6¼"	7"	9¼" W, 4½" H

For flush mount options, see pages 24-26.

Brooke's updated traditional look features a minimalist forged scroll design in Olde Bronze that elegantly complements its etched opal glass.

FINISH OLDE BRONZE
GLASS ETCHED OPAL

BROOKE™

ADDITIONAL FINISHES
Antique Nickel (AN), Silver Leaf (SL)



5003 OB
24" W, 10¾" H



5000 OB
5¼" W, 11¾" H



3782 OZ
13¾" DIA., 5" H



5002 OB
16½" W, 10¼" H



5004 OB
31¼" W, 11" H



5005 OB
41½" W, 11" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3782 OZ*	2-40w Med.			
5000 OB	1-100w Incan. or 1-17w LED Med.	5½"	8"	4½" W, 7¼" H
5002 OB	2-100w Incan. or 2-17w LED Med.	6¼"	6½"	9¼" W, 4½" H
5003 OB	3-100w Incan. or 3-17w LED Med.	6¼"	7¼"	9¼" W, 4½" H
5004 OB	4-100w Incan. or 4-17w LED Med.	6¼"	7"	9¼" W, 4½" H
5005 OB	5-100w Incan. or 5-17w LED Med.	6¼"	7"	9¼" W, 4½" H

*Recommended companion flush mount. For additional options, see pages 24-26.

BROOKE™

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL

Brooke's updated traditional look features a minimalist forged scroll design in Antique Nickel that elegantly complements its etched opal glass.

ADDITIONAL FINISHES

Olde Bronze (OB), Silver Leaf (SL)



3782 AN
13¾" DIA., 5" H



5000 AN
5¼" W, 11¾" H



5003 AN
24" W, 10¾" H



5004 AN
31¼" W, 11" H



5002 AN
16½" W, 10¼" H



5005 AN
41½" W, 11" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
3782 AN*	2-40w Med.			
5000 AN	1-100w Incan. or 1-17w LED Med.	5½"	8"	4½" W, 7¼" H
5002 AN	2-100w Incan. or 2-17w LED Med.	6¼"	6½"	9¼" W, 4½" H
5003 AN	3-100w Incan. or 3-17w LED Med.	6¼"	7¼"	9¼" W, 4½" H
5004 AN	4-100w Incan. or 4-17w LED Med.	6¼"	7"	9¼" W, 4½" H
5005 AN	5-100w Incan. or 5-17w LED Med.	6¼"	7"	9¼" W, 4½" H

*Recommended companion flush mount. For additional options, see pages 24-26.

Reese features a traditional design with boutique details. The etched opal glass and Antique Nickel finish is updated with elegant, laser cut scrolls for a modern touch.

FINISH ANTIQUE NICKEL
GLASS ETCHED OPAL

REESE™



3782 AN
13¾" DIA., 5" H



56320 AN
(shown with scrollwork reversed)



56322 AN
20½" W, 9" H



56320 AN
5" W, 13½" H



56323 AN
24" W, 9¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	INV
3782 AN*	2-40w Med.				
56320 AN	1-100w Incan. or 1-17w LED Med.	6¾"	9¾"	5" Dia.	
56322 AN	2-100w Incan. or 2-17w LED Med.	7"	6¾"	5" Dia.	•
56323 AN	3-100w Incan. or 3-17w LED Med.	7"	6½"	5" Dia.	•

*Recommended companion flush mount. For additional options, see pages 24-26.

FRANCOISE™

FINISH POLISHED ANTIQUE NICKEL
GLASS FROSTED RIBBED

Francoise offers a European elegance with decorative cast detailing in Polished Antique Nickel or Burnished Brass finish options. The frosted ribbed glass adds to its classical appeal.

ADDITIONAL FINISHES

Burnished Brass (BB)



5582 PL
15" W, 9½" H



5583 PL
25¼" W, 9½" H



5580 PL
6" W, 10¾" H



5584 PL
31" W, 9½" H



5585 PL
37" W, 9½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5580 PL	1-100w Incan. or 1-17w LED Med.	6¾"	6¼"	4½" W, 9¼" H
5582 PL	2-100w Incan. or 2-17w LED Med.	6¾"	7¼"	9¼" W, 4½" H
5583 PL	3-100w Incan. or 3-17w LED Med.	6¾"	7¼"	9¼" W, 4½" H
5584 PL	4-100w Incan. or 4-17w LED Med.	6¾"	7¼"	9¼" W, 4½" H
5585 PL	5-100w Incan. or 5-17w LED Med.	6¾"	7¼"	9¼" W, 4½" H

For flush mount options, see pages 24-26.

Francoise offers a European elegance with decorative cast detailing in Polished Antique Nickel or Burnished Brass finish options. The frosted ribbed glass adds to its classical appeal.

FINISH BURNISHED BRASS
GLASS FROSTED RIBBED

FRANCOISE™

ADDITIONAL FINISHES
Polished Antique Nickel (PL)



5583 BB
25¼" W, 9½" H



5582 BB
15" W, 9½" H



5584 BB
31" W, 9½" H



5580 BB
6" W, 10¾" H



5585 BB
37" W, 9½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
5580 BB	1-100w Incan. or 1-17w LED Med.	6¾"	6¼"	4½" W, 9¼" H
5582 BB	2-100w Incan. or 2-17w LED Med.	6¾"	7¼"	9¼" W, 4½" H
5583 BB	3-100w Incan. or 3-17w LED Med.	6¾"	7¼"	9¼" W, 4½" H
5584 BB	4-100w Incan. or 4-17w LED Med.	6¾"	7¼"	9¼" W, 4½" H
5585 BB	5-100w Incan. or 5-17w LED Med.	6¾"	7¼"	9¼" W, 4½" H

For flush mount options, see pages 24-26.

CASA™

FINISH OLDE BLACK
GLASS CLEAR SEEDY

Casa makes the most of its fine details: clear seedy glass, twisted wrought iron and hand-forged scrollwork in an Olde Black finish complete its rustic-chic appeal with a Southwestern flair.

Casa Interior, pages 266-271

ADDITIONAL FINISHES

Olde Black (OL)



5543 OL-CL
22¾" W, 9¼" H



5542 OL-CL
15¾" W, 9¼" H



4300 OL-CL
5¼" W, 23" H



4010 OL-CL
5¼" W, 11¼" H



5544 OL-CL
29¼" W, 9¼" H



5545 OL-CL
35¾" W, 9¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
4010 OL-CL	1-100w Med.	6"	7¼"	5¼" W, 7¾" H
4300 OL-CL	1-100w Med.	4¼"	10"	5¼" W, 7¾" H
5542 OL-CL	2-100w Med.	7"	3¾"	7½" W, 5" H
5543 OL-CL	3-100w Med.	7"	3¾"	7½" W, 5" H
5544 OL-CL	4-100w Med.	7"	3¾"	7½" W, 5" H
5545 OL-CL	5-100w Med.	7"	3¾"	7½" W, 5" H

Casa bath fixtures can be mounted facing up or down. For flush mount options, see pages 24-26.

Casa makes the most of its fine details: individually unique antique scavo glass, twisted wrought iron and hand-forged scrollwork in an Olde Black finish complete its rustic-chic appeal with a Southwestern flair.
Casa Interior, pages 266-271


FINISH OLDE BLACK
GLASS ANTIQUE SCAVO

CASA™

ADDITIONAL FINISHES
Olde Black with Clear Seedy glass (OL-CL)



5542 OL
15¾" W, 8¾" H



5543 OL
22¾" W, 8¾" H




5544 OL
29¼" W, 8¾" H



4010 OL
5" W, 10¾" H



4300 OL
5" W, 24" H



5545 OL
35¾" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
4010 OL	1-100w Incan. or 1-17w LED Med.	6"	6¾"	5" W, 7¾" H
4300 OL	1-100w Incan. or 1-17w LED Med.	4¼"	11¼"	5" W, 7¾" H
5542 OL	2-100w Incan. or 2-17w LED Med.	7"	3¼"	7½" W, 5" H
5543 OL	3-100w Incan. or 3-17w LED Med.	7"	3¼"	7½" W, 5" H
5544 OL	4-100w Incan. or 4-17w LED Med.	7"	3¼"	7½" W, 5" H
5545 OL	5-100w Incan. or 5-17w LED Med.	7"	3¼"	7½" W, 5" H

Casa bath fixtures can be mounted facing up or down. For flush mount options, see pages 24-26.

PLANTATION™

FINISH POLISHED ANTIQUE NICKEL
GLASS CLEAR OPTIC

A Hinkley classic, the ornate Plantation collection features exceptional pineapple-shaped, clear optic glass that makes a noble statement. The elaborate, decorative cast detailing is accentuated by its lush finish.

Plantation Interior, pages 284-291

ADDITIONAL FINISHES

Burnished Brass (BB)



4102 PL
12" DIA., 8" H



4881 PL
16" DIA., 8¾" H



5312 PL
13" W, 8¾" H



5313 PL
21" W, 8¾" H



5314 PL
29" W, 8¾" H



5310 PL
5" W, 8¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
4102 PL	2-60w Med.			
4881 PL	3-60w Med.			
5310 PL	1-100w Med.	6½"	4¾"	4¾" W, 8" H
5312 PL	2-100w Med.	6¾"	4¾"	8" W, 4¾" H
5313 PL	3-100w Med.	6½"	4¾"	8" W, 4¾" H
5314 PL	4-100w Med.	6¾"	4¾"	8" W, 4¾" H

Plantation bath fixtures can be mounted facing up or down.

A Hinkley classic, the ornate Plantation collection features exceptional pineapple-shaped, clear optic glass that makes a noble statement. The elaborate, decorative cast detailing is accentuated by its lush finish.

Plantation Interior, pages 284-291

FINISH BURNISHED BRASS
GLASS CLEAR OPTIC

PLANTATION™

ADDITIONAL FINISHES
Polished Antique Nickel (PL)



4881 BB
16" DIA., 8¾" H



4102 BB
12" DIA., 8" H



5313 BB
21" W, 8¼" H



5312 BB
13" W, 8¼" H



5310 BB
5" W, 8¾" H



5314 BB
29" W, 8¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
4102 BB	2-60w Med.			
4881 BB	3-60w Med.			
5310 BB	1-100w Med.	6½"	4¾"	4¾" W, 8" H
5312 BB	2-100w Med.	6¾"	4¾"	8" W, 4¾" H
5313 BB	3-100w Med.	6½"	4¾"	8" W, 4¾" H
5314 BB	4-100w Med.	6¾"	4¾"	8" W, 4¾" H

Plantation bath fixtures can be mounted facing up or down.

SAN SIMEON™

FINISH SILVER LEAF
GLASS HAND-PAINTED FAWN

The San Simeon collection combines angular lines with traditional forms featuring an authentic hand-applied Silver Leaf finish and beautifully painted fawn colored glass.



FR49190SLF
6" W, 24½" H



FR59192SLF
14½" W, 9¾" H



FR59193SLF
24" W, 9¾" H



FR59194SLF
33½" W, 9¾" H


ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
FR49190SLF	1-100w Incan. or 1-17w LED Med.	8½"	11½"	6" Square
FR59192SLF	2-100w Incan. or 2-17w LED Med.	6½"	7¼"	13" W, 5" H
FR59193SLF	3-100w Incan. or 3-17w LED Med.	6½"	7¼"	13" W, 5" H
FR59194SLF	4-100w Incan. or 4-17w LED Med.	6½"	7¼"	13" W, 5" H

For flush mount options, see pages 24-26.

WHY WE ♥ AN INDUSTRIAL BATH

Something about this unpretentious style and pared down design just makes us feel good:

- + Deceptively simple lines, with unassuming touches that project a unique combination of sophistication and durability.
- + Bold finishes that feel both raw and refined, easily mixing with a variety of hardware and tile.



LISA MCDENNON
LISA MCDENNON DESIGN
LAGUNA BEACH, CA

"I love to mix finishes in the bathroom, and it's actually better to mix it up so that the room does not become boring. Think of it like putting together an outfit — we mix styles together and choose items that coordinate, and thus create a cohesive, yet unique look."

ABOVE: THE JACKSON COLLECTION | 51822BN, PAGE 372



“As a landscape designer I always design the lighting to convey a welcoming feeling. There is nothing like coming up a drive through an up-lit grove of trees, a beautifully washed wall, or the path light that guides you to the front door.”



NICK MCCULLOUGH
MCCULLOUGH'S LANDSCAPE
AND NURSERY
COLUMBUS, OH

ABOVE: THE PORTER COLLECTION | 2805DZ, PAGE 572 AND
THE NUVI COLLECTION | 15446BZ, PAGE 668
OPPOSITE PAGE: THE PORTER COLLECTION | 2805DZ, PAGE 572

OUTDOOR COLLECTIONS



ADAIR	576	CARSON	440	LEDGEWOOD	518	PORTER	572	TATUM	570
ALFORD PLACE	596	CASA	614	LEX	460	QUINCY	530	THATCHER	545
ANCHORAGE	578	CASCADE	470	LINCOLN	594	RALEY	628	THEO	537
ARIA	484	CASTELLE	520	LUCERNE	662	RANDOLPH	524	TITAN	471
ATLANTIS	472	CHERRY CREEK	514	LUNA	462	REEF	552	TRAFALGAR	638
ATWELL	438	CLIFTON PARK	660	MANHATTAN	504	REGAL	645	TRELLIS	598
AUGUSTA	658	COLFAX	502	MANOR HOUSE	642	REVERE	590	TROYER	436
BARRINGTON	627	DORIAN	480	MARINA	554	RILEY	532	TUCKER	522
BECKETT	433	EDGEWATER	646	MIST	450	SAN CLEMENTE	652	VAPOR	448
BELDEN PLACE	569	ENZO	608	MONDRIAN	533	SATURN	496	VISTA	455
BINGHAM	584	FREEPORT	556	MONTAUK	589	SAYBROOK	568	VUE	454
BOLLA	610	GLACIER	446	MONTICELLO	656	SEDGWICK	593	WABASH	640
BRIGGS	571	HADLEY	528	NANTUCKET	588	SENATOR	641	WALKER	540
BROMLEY	604	HARBOR	508	NEW CASTLE	560	SHELTER	488	WESTPORT	549
BURKE	538	HORIZON	494	NEWPORT	548	SORRENTO	618	WESTWINDS	624
BURTON	544	HUDSON	529	OXFORD	636	SULLIVAN	534	WINDSOR	632
CALISTOGA	563	KEY WEST	650	PERRY	550	SURF	456	YORK	582
CAMELOT	644	KORE	468	PLANTATION	620	SUTCLIFFE	546		
CAPE COD	564	KUBE	479	PLAZA	453	TAHOE	526		

GET OUT

AND ENJOY THE VIEW

"Lighting fixtures tie the design together and take a garden from a daytime experience and transition it into a relaxing retreat that can be enjoyed well into the evening. There are always two elements that catch my eye when selecting fixtures: sleek modern lines and quality material. It needs to be simple and elegant but also stand up to the conditions of being outside."



NICK MCCULLOUGH
MCCULLOUGH'S LANDSCAPE
AND NURSERY
COLUMBUS, OH

ALFRESCO ABODE

Nothing conveys confidence and the sense of satisfaction you get from your home more than seeing your personal style radiate all the way through to the exterior spaces. Curate your outdoor living areas by selecting sophisticated lighting that reinforces your home's architecture and illuminates gatherings with the glow of personal panache.








MODERN CONCEPT

illuminating a **CONTEMPORARY CASA**

The most fabulous façades showcase lighting fixtures that make a cohesive style statement while reinforcing architectural integrity. Select lanterns and decorative path lights with sleek profiles and streamlined silhouettes that will maximize your minimalist look from day to night.

ABOVE: LUNA 1669SK, PAGE 463 | SHELTER 15607HE,
SEE HINKLEYLIGHTING.COM. RIGHT: SHELTER 1321KZ,
PAGE 491 AND 1547KZ, SEE HINKLEYLIGHTING.COM





KELLY DECK
 KELLY DECK DESIGN
 VANCOUVER, BC

“People love the ocean—the seaside, sailing, boating; it all evokes an idea of freedom and adventure. It is elegant and restrained and translates beautifully into lighting and objects for the home.

ABOVE: PERRY 2384OZ, PAGE 550 | MARINA 2410HE, PAGE 555 | WESTPORT 2722DZ, PAGE 549



BEACON OF STYLE

navigate toward lanterns with coastal character

LEFT: BELDEN PLACE 2864OZ, PAGE 569 | NEWPORT 2624DZ, PAGE 548
 BRIGGS 2490KZ, PAGE 571 | SAYBROOK 2344OZ, PAGE 568
 FREEPORT 1804CW, PAGE 556

BRINGING THE INDOORS OUT...



OPEN AIR

As the design movement to create a seamless transition between a home's interior and exterior continues, Hinkley's collection of outdoor-rated chandeliers has grown. These stunning new fixtures are appropriate for any exterior space—a dining terrace, backyard pergola or front porch.

LOOK FOR THE ABOVE OPEN AIR ICON TO FIND THE PERFECT INTERIOR-INSPIRED PIECE TO ILLUMINATE YOUR ALFRESCO AREA.

THE CARSON COLLECTION
29705VI AND 29700VI, PAGE 442

...AND THE OUTDOORS IN



ATWELL 1112OZ



WALKER 2102KZ



COLFAX 2922PS

Think outside the house! Exterior fixtures may offer the statement you've been searching for. A few of our favorite pendants look equally at home over a bar or kitchen island as they do outdoors.

AS AN ADDED BONUS, EXTERIOR FIXTURES OFTEN BOAST MORE ECO-FRIENDLY CONFIGURATIONS!

Bring beauty outdoors with Beckett's combination of vintage industrial and rustic design elements. This durable, stem hung chandelier is wet-rated and constructed in resilient coated steel. A sturdy mesh drum shade and coated faux wood accents combine with an Iron Rust finish and clear seedy glass for the ultimate in modern farmhouse style. A subtly designed center down light offers an additional, functional light source for evenings alfresco.

FINISH IRON RUST
GLASS CLEAR SEEDY
SHADE MESH

BECKETT™

OPEN AIR 
collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES



29616 IR
30" DIA., 27" H
61" MAX. H*

ITEM	MAXIMUM WATTAGE	CANOPY	WIRE	STEMS INCLUDED
29616 IR	4-100w Med., 1-35w GU-10**	5¼" Dia. Canopy	10'	1-6, 2-12

*Maximum achievable height with stems included. Additional 12" stems available, 6033 IN. **GU-10 bulb for downlight included. Ideal for vintage filament bulbs (not included).

SAWYER™

FINISH SEQUOIA
GLASS CLEAR SEEDY, ETCHED

The fresh, rustic design of the Sawyer collection will inject any outdoor living experience with the warm, cozy ambiance of an indoor setting. Constructed with Hinkley's own anti-corrosion coating, the faux wood finish over coated steel ensures maximum resiliency and performance in the elements.

 **OPEN AIR**
collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES



29208 SQ
30" DIA., 27¾" H



29206 SQ
24" DIA., 23¼" H



29203 SQ
15" DIA., 4¾" H



29201 SQ
9" DIA., 4½" H



29202 SQ
9" W, 12" H



29205 SQ
42" W, 7¾" H

ITEM	MAXIMUM WATTAGE	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
29201 SQ	2-40w Cand.				8¼" Dia. Canopy	
29202 SQ	2-60w Cand.		2¾"	2¼"	4½" Square Back Plate	
29203 SQ	3-40w Cand.				14" Dia. Canopy	
29205 SQ	5-60w Cand.	3½"			12¾" L, 4¾" W Canopy	10', 5'
29206 SQ	6-60w Cand.				5¼" Dia. Canopy	10', 5'
29208 SQ	9-60w Cand.				5¼" Dia. Canopy	10', 5'

Ideal for vintage filament bulbs (not included).

TROYER™

FINISH AGED ZINC, BLACK,
OIL RUBBED BRONZE
GLASS CLEAR RIBBED


Troyer's authentic outdoor collection captures the enduring allure of American farmhouse lighting. Constructed in solid aluminum, Troyer's warm and inviting heritage details combine with unique ribbed glass accent and timeless finishes for a classic silhouette.

 **OPEN AIR**
collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES



1192 OZ
10" DIA., 7½" H
40" MAX. H*



1192 DZ
10" DIA., 7½" H
40" MAX. H*



1192 BK
10" DIA., 7½" H
40" MAX. H*



1194 DZ
10" W, 10" H



1194 BK
10" W, 10" H



1194 OZ
10" W, 10" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
1192 BK	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
1192 DZ	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
1192 OZ	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
1194 BK	1-100w Med.	11"	5½"	5" Dia. Back Plate		
1194 DZ	1-100w Med.	11"	5½"	5" Dia. Back Plate		
1194 OZ	1-100w Med.	11"	5½"	5" Dia. Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available. For 1192 BK, use 6064 BKOD. For 1192 DZ, use 6064 DZOD. For 1192 OZ, use 6064 OZOD.

ATWELL™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Industrial-inspired Atwell recalls turn-of-the-century American factory lighting. Aged Zinc and Oil Rubbed Bronze finish options reinforce its vintage silhouette. Clear seedy glass, cast glass holder and authentic details like gooseneck arms and bespoke back plate and canopy enhance Atwell's nostalgic appeal.

 **OPEN AIR**
collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES

ADDITIONAL FINISHES
Aged Zinc (DZ)



1110 OZ
11½" W, 11¾" H



1113 OZ
24¼" DIA., 10¼" H
45½" MAX. H*



1114 OZ
14½" W, 15¼" H



1112 OZ
14½" DIA., 11" H
44" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
1110 OZ	1-60w Med.	13"	4¾"	5" Dia. Back Plate		
1112 OZ	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
1113 OZ	3-60w Med.			6" Dia. Canopy	10'	1-6", 2-12"
1114 OZ	1-100w Med.	16"	5¼"	6" Dia. Back Plate		

*Maximum achievable height with stems included. Additional stems available. For 1112 OZ use 6037 OZOD, and for 1113 OZ use 6067 OZOD. Ideal for vintage filament bulbs (not included).

Industrial-inspired Atwell recalls turn-of-the-century American factory lighting. Aged Zinc and Oil Rubbed Bronze finish options reinforce its vintage silhouette. Clear seedy glass, cast glass holder and authentic details like gooseneck arms and bespoke back plate and canopy enhance Atwell's nostalgic appeal.

FINISH AGED ZINC
GLASS CLEAR SEEDY

ATWELL™

OPEN AIR 
collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



1112 DZ
14½" DIA., 11" H
44" MAX. H*



1113 DZ
24¼" DIA., 10¼" H
45½" MAX. H*



1110 DZ
11½" W, 11¾" H



1114 DZ
14½" W, 15¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
1110 DZ	1-60w Med.	13"	4¾"	5" Dia. Back Plate		
1112 DZ	1-100w Med.			5" Dia. Canopy	10'	1-6", 2-12"
1113 DZ	3-60w Med.			6" Dia. Canopy	10'	1-6", 2-12"
1114 DZ	1-100w Med.	16"	5¼"	6" Dia. Back Plate		

*Maximum achievable height with stems included. Additional stems available. For 1112 DZ use 6037 DZOD, and for 1113 DZ use 6067 DZOD. Ideal for vintage filament bulbs (not included).

CARSON™

FINISH WEATHERED ZINC
GLASS CLEAR SEEDY

Carson features bold overlapping metal ribbons of Vintage Iron or Weathered Zinc, enhancing an outdoor living area with style and substance. The hand-crafted pendants combine a hint of industrial sophistication with the allure of artisan craftsmanship.

 **OPEN AIR**
collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES

ADDITIONAL FINISHES
Vintage Iron (VI)



29705 WZ
26½" DIA., 26¼" H
61¾" MAX. H*



29703 WZ
18½" DIA., 18¾" H
54¼" MAX. H*



29700 WZ
10" W, 10½" H



29707 WZ
10" DIA., 10½" H
46" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
29700 WZ	1-100w Med.	12¼"	6"	4¾" Dia. Back Plate		
29703 WZ	3-60w Cand.			4¾" Dia. Canopy	12'	1-6", 2-12"
29705 WZ	5-60w Cand.			4¾" Dia. Canopy	12'	1-6", 2-12"
29707 WZ	1-100w Med.			4¾" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional stems available. For 29703 WZ and 29705 WZ use 6063 WZ. For 29707 WZ use 6033 WZ. Ideal for vintage filament bulbs (not included).

CARSON™

FINISH VINTAGE IRON
GLASS CLEAR SEEDY

Carson features bold overlapping metal ribbons of Vintage Iron or Weathered Zinc, enhancing an outdoor living area with style and substance. The hand-crafted pendants combine a hint of industrial sophistication with the allure of artisan craftsmanship.

 **OPEN AIR**
collection

CHIC DESIGNS RATED FOR USE IN BOTH
INTERIOR AND EXTERIOR SPACES

ADDITIONAL FINISHES
Weathered Zinc (WZ)



29705 VI
26½" DIA., 26¼" H
61¾" MAX. H*



29703 VI
18½" DIA., 18¾" H
54¼" MAX. H*



29700 VI
10" W, 10½" H



29707 VI
10" DIA., 10½" H
46" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED
29700 VI	1-100w Med.	12½"	6"	4¾" Dia. Back Plate		
29703 VI	3-60w Cand.			4¾" Dia. Canopy	12'	1-6", 2-12"
29705 VI	5-60w Cand.			4¾" Dia. Canopy	12'	1-6", 2-12"
29707 VI	1-100w Med.			4¾" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional stems available. For 29703 VI and 29705 VI use 6063 VI. For 29707 VI use 6033 VI. Ideal for vintage filament bulbs (not included).





AIM HIGH

You can have it all. Dynamic design brings flair and function to a space, complemented by lighting that offers solutions with style.

For spaces with safety requirements, such as ample clearance, ADA sconces (Americans With Disabilities Act) are thoughtfully designed to ensure minimal protrusion from walls. For a full range of our ADA products, please refer to pages 22-23 in the pictorial index.



VAPOR 2854TT



SAWYER 29202SQ



LUNA 1659SK



SATURN 1908SS



HORIZON 2890BK



PLAZA 20305BZ

LEFT: THE VUE COLLECTION | 12314BZ, PAGE 454

GLACIER™

FINISH BRONZE, TITANIUM
GLASS CLEAR SEEDY

Glacier's impressive form merges industrial and contemporary design elements into a breath-taking silhouette. A substantial block of clear seedy glass with etched grooves brilliantly channels light from the high-performance LED, which is held in suspension by the powder-coated aluminum frame.



exclusively available in
HIGH-PERFORMANCE LED



2835 TT
4¾" W, 28" H
  



2835 BZ
4¾" W, 28" H
  



2830 TT
4¾" W, 15½" H



2830 BZ
4¾" W, 15½" H



2834 TT
(side view)



2834 TT
4¾" W, 22" H



2834 BZ
4¾" W, 22" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
2830 BZ	15w LED	800	2700K	91	1-60w	4"	7¾"	4¾" Square
2830 TT	15w LED	800	2700K	91	1-60w	4"	7¾"	4¾" Square
2834 BZ	15w LED	800	2700K	91	1-60w	4"	11"	4¾" Square
2834 TT	15w LED	800	2700K	91	1-60w	4"	11"	4¾" Square
2835 BZ	15w LED	800	2700K	91	1-60w	4"	14"	4¾" Square
2835 TT	15w LED	800	2700K	91	1-60w	4"	14"	4¾" Square

For full product details and LED specifications, refer to hinkleylighting.com.

VAPOR™

FINISH BRONZE, TITANIUM
GLASS CRACKLE

Vapor's streamlined profile allows the spectacular crackled glass to star in this captivating design. The low profile back plate and stamped metal construction project a sleek, contemporary style statement.



2855 BZ
4¾" W, 28" H



2855 TT
4¾" W, 28" H





2850 BZ
4¾" W, 14" H



2850 TT
4¾" W, 14" H





**DESIGN
NOTE**

VAPOR'S CRACKLED
GLASS PATTERN
IS EVEN MORE
DECORATIVE IN THE
DARK, CREATING
ADDED INTEREST
AT NIGHT.



2854 BZ
4¾" W, 21" H



2854 TT
4¾" W, 21" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2850 BZ	1-35w GU10*	3¾"	7¼"	4¾" Square
2850 TT	1-35w GU10*	3¾"	7¼"	4¾" Square
2854 BZ	1-35w GU10*	3¾"	10½"	4¾" Square
2854 TT	1-35w GU10*	3¾"	10½"	4¾" Square
2855 BZ	1-35w GU10*	3¾"	14¼"	4¾" Square
2855 TT	1-35w GU10*	3¾"	14¼"	4¾" Square

*GU10 bulb included.

MIST™

FINISH TITANIUM
 GLASS CLEAR ACRYLIC
 OUTSIDE CYLINDER,
 SEEDY GLASS INSIDE PANEL

The sleek design of the Mist collection discreetly emphasizes its contemporary heritage. Featuring a prominent interior panel of clear seedy glass captured on both ends and encased in a protective clear acrylic cylinder. Its solid aluminum construction is underscored by bold Satin Black, Bronze or Titanium finish options. Mist is both Dark Sky and ADA compliant.

ADDITIONAL FINISHES

Bronze (BZ), Satin Black (SK)



1225 TT
 4¾" W, 28½" H

☾ ♿



1220 TT
 4¾" W, 15½" H

☾ ♿



1224 TT
 4¾" W, 22" H

☾ ♿

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
1220 TT	1-35w GU-10	4"	7¾"	4¾" Square
1224 TT	1-35w GU-10	4"	11"	4¾" Square
1225 TT	1-35w GU-10	4"	14¼"	4¾" Square

The sleek design of the Mist collection discreetly emphasizes its contemporary heritage. Featuring a prominent interior panel of clear seedy glass captured on both ends and encased in a protective clear acrylic cylinder. Its solid aluminum construction is underscored by bold Satin Black, Bronze or Titanium finish options. Mist is both Dark Sky and ADA compliant.

FINISH BRONZE
GLASS CLEAR ACRYLIC
OUTSIDE CYLINDER,
SEEDY GLASS INSIDE PANEL

MIST™

ADDITIONAL FINISHES
Satin Black (SK), Titanium (TT)



1224 BZ
4¾" W, 22" H
☾ ♿



1220 BZ
4¾" W, 15½" H
☾ ♿



1225 BZ
4¾" W, 28½" H
☾ ♿

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
1220 BZ	1-35w GU-10	4"	7¾"	4¾" Square
1224 BZ	1-35w GU-10	4"	11"	4¾" Square
1225 BZ	1-35w GU-10	4"	14¼"	4¾" Square

MIST™

FINISH SATIN BLACK
 GLASS CLEAR ACRYLIC
 OUTSIDE CYLINDER,
 SEEDY GLASS INSIDE PANEL

The sleek design of the Mist collection discreetly emphasizes its contemporary heritage. Featuring a prominent interior panel of clear seedy glass captured on both ends and encased in a protective clear acrylic cylinder. Its solid aluminum construction is underscored by bold Satin Black, Bronze or Titanium finish options. Mist is both Dark Sky and ADA compliant.

ADDITIONAL FINISHES
 Bronze (BZ), Titanium (TT)



1225 SK
 4¾" W, 28½" H

☾ ♿



1220 SK
 4¾" W, 15½" H

☾ ♿



1224 SK
 4¾" W, 22" H

☾ ♿

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
1220 SK	1-35w GU-10	4"	7¾"	4¾" Square
1224 SK	1-35w GU-10	4"	11"	4¾" Square
1225 SK	1-35w GU-10	4"	14¼"	4¾" Square

Plaza features a contemporary form constructed from durable aluminum. This sleek shape creates a unique wall-wash effect with a down light producing a subtle interior grazing for a layered sense of illumination.

FINISH BRONZE, TITANIUM
GLASS ETCHED ACRYLIC LENS

PLAZA™


exclusively available in
HIGH-PERFORMANCE LED 



20305 TT
7" W, 20" H
 





20305 BZ
7" W, 20" H
 



20300 BZ
10" W, 10" H
 



20300 TT
10" W, 10" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
20300 BZ	24w LED	1900	2700K	90	2-75w	4"	5"	6¼" Square
20300 TT	24w LED	1900	2700K	90	2-75w	4"	5"	6¼" Square
20305 BZ	22w LED	1950	2700K	90	2-75w	4"	10"	5" W, 15¼" H
20305 TT	22w LED	1950	2700K	90	2-75w	4"	10"	5" W, 15¼" H

For full product details and LED specifications, refer to hinkleylighting.com.

VUE™

FINISH BRONZE, TITANIUM
GLASS ACRYLIC LENS

Vue's contemporary linear LED design is constructed of extruded and die-cast aluminum and is offered in either Bronze or Titanium finishes. The seamless architectural form emits light from white acrylic side windows and sleek front sliver. Incredibly versatile, the wet-rated Vue can be mounted vertically or horizontally, inside or outdoors.

 exclusively available in
HIGH-PERFORMANCE LED



12312 TT
(mounted horizontally)



12312 BZ
5" W, 14¾" H



12314 BZ
5" W, 26" H



12312 TT
5" W, 14¾" H



12314 TT
5" W, 26" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
12312 BZ	15w LED	1200	2700K	90	2-60w	3"	7½"	5" W, 6" H
12312 TT	15w LED	1200	2700K	90	2-60w	3"	7½"	5" W, 6" H
12314 BZ	30w LED	2400	2700K	90	4-60w	3"	13"	5" W, 6" H
12314 TT	30w LED	2400	2700K	90	4-60w	3"	13"	5" W, 6" H

For full product details and LED specifications, refer to hinkleylighting.com.

Vista creates a strong visual statement with an elongated contemporary silhouette. Constructed with extruded and die-cast aluminum, an angled cut-out creates a modern focal point with a resilient acrylic lens for maximum durability. Vista is offered as an energy-saving LED design in either Bronze or Titanium finish options. Incredibly versatile, the wet-rated Vista can be mounted vertically or horizontally, inside or outdoors.

FINISH BRONZE, TITANIUM
GLASS ACRYLIC LENS

VISTA™

exclusively available in
HIGH-PERFORMANCE LED 



12302 BZ
(mounted horizontally)



12302 BZ
5" W, 18¾" H



12304 BZ
5" W, 29½" H



12302 TT
5" W, 18¾" H



12304 TT
5" W, 29½" H




LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
12302 BZ	15w LED	1200	2700K	90	2-60w	3"	9½"	5" W, 6" H
12302 TT	15w LED	1200	2700K	90	2-60w	3"	9½"	5" W, 6" H
12304 BZ	30w LED	2400	2700K	90	4-60w	3"	14¾"	5" W, 6" H
12304 TT	30w LED	2400	2700K	90	4-60w	3"	14¾"	5" W, 6" H

For full product details and LED specifications, refer to hinkleylighting.com.

SURF™



FINISH SATIN BLACK

Surf's chic design reflects the natural curl of a breaking wave. Constructed of solid aluminum, this LED lantern emits light both up and down. Surf is finished with marine grade powder coat for maximum durability.



 exclusively available in
HIGH-PERFORMANCE LED

ADDITIONAL FINISHES
Bronze (BZ), Stainless Steel (SS), Titanium (TT)



2354 SK
8¼" W, 19" H
 

2355 SK
10¼" W, 24" H
 

2350 SK
6¼" W, 15" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
2350 SK	20w LED	950	2700K	91	2-60w	5½"	8¾"	4½" W, 7½" H
2354 SK	26w LED	1300	2700K	91	2-75w	6¼"	11"	4½" W, 7½" H
2355 SK	30w LED	1600	2700K	91	2-100w	8"	14"	5" W, 11½" H

For full product details and LED specifications, refer to hinkleylighting.com.


Surf's chic design reflects the natural curl of a breaking wave. Constructed of stainless steel, this LED lantern emits light both up and down. Surf is finished with marine grade powder coat for maximum durability.

FINISH TITANIUM

SURF™

exclusively available in
HIGH-PERFORMANCE LED 

ADDITIONAL FINISHES
Bronze (BZ), Satin Black (SK), Stainless Steel (SS)




LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
2350 TT	20w LED	950	2700K	91	2-60w	5½"	8¾"	4½" W, 7½" H
2354 TT	26w LED	1300	2700K	91	2-75w	6¼"	11"	4½" W, 7½" H
2355 TT	30w LED	1600	2700K	91	2-100w	8"	14"	5" W, 11½" H

For full product details and LED specifications, refer to hinkleylighting.com.

SURF™

FINISH BRONZE

Surf's chic design reflects the natural curl of a breaking wave. Constructed of solid aluminum, this LED lantern emits light both up and down. Surf is finished with marine grade powder coat for maximum durability.

 exclusively available in
HIGH-PERFORMANCE LED

ADDITIONAL FINISHES

Satin Black (SK), Stainless Steel (SS), Titanium (TT)



2354 BZ
8¼" W, 19" H
 



2355 BZ
10¼" W, 24" H
 



2350 BZ
6¼" W, 15" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
2350 BZ	20w LED	950	2700K	91	2-60w	5½"	8¾"	4½" W, 7½" H
2354 BZ	26w LED	1300	2700K	91	2-75w	6¼"	11"	4½" W, 7½" H
2355 BZ	30w LED	1600	2700K	91	2-100w	8"	14"	5" W, 11½" H

For full product details and LED specifications, refer to hinkleylighting.com.


Surf's chic design reflects the natural curl of a breaking wave. Constructed of stainless steel, this LED lantern emits light both up and down. Surf is finished with marine grade powder coat for maximum durability.

FINISH STAINLESS STEEL

SURF™

exclusively available in
HIGH-PERFORMANCE LED 

ADDITIONAL FINISHES
Bronze (BZ), Satin Black (SK), Titanium (TT)



2350 SS
6¼" W, 15" H
 

2355 SS
10¼" W, 24" H
 

2354 SS
8¼" W, 19" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
2350 SS	20w LED	950	2700K	91	2-60w	5½"	8¾"	4½" W, 7½" H
2354 SS	26w LED	1300	2700K	91	2-75w	6¼"	11"	4½" W, 7½" H
2355 SS	30w LED	1600	2700K	91	2-100w	8"	14"	5" W, 11½" H

For full product details and LED specifications, refer to hinkleylighting.com.

LEX™

FINISH BRONZE, STAINLESS STEEL

Lex is a lantern formed out of geometric shapes that embodies modern design. Architectural in look and feel, Lex offers a striking silhouette in durable aluminum and solid stainless steel construction combined with LED technology for a bold contemporary statement.

 exclusively available in
HIGH-PERFORMANCE LED




2715 BZ
10½" W, 22" H
 



2714 BZ
8½" W, 15" H
 



2715 SS
10½" W, 22" H
 



2714 SS
8½" W, 15" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
2714 BZ	15w LED	800	2700K	96	1-100w	5"	7½"	4½" W, 6¾" H
2714 SS	15w LED	800	2700K	96	1-100w	5"	7½"	4½" W, 6¾" H
2715 BZ	15w LED	800	2700K	96	1-100w	5½"	11"	4½" W, 6¾" H
2715 SS	15w LED	800	2700K	96	1-100w	5½"	11"	4½" W, 6¾" H

For full product details and LED specifications, refer to hinkleylighting.com.



LUNA™

FINISH BRONZE, SATIN BLACK,
SATIN WHITE, TITANIUM
GLASS ETCHED GLASS LENS

Luna is a modern collection of solid aluminum fixtures offered in a unique combination of contemporary styles, including sleek wall lanterns. Luna also offers chic pocket wall sconces and compact ceiling mounts that are ideal for indoor or out.



1669 TT
1669 TT-LED
9" W, 24" H





1669 SK
1669 SK-LED
9" W, 24" H



1669 BZ
1669 BZ-LED
9" W, 24" H



1668 TT
1668 TT-LED
6" W, 16¼" H



1668 SK
1668 SK-LED
6" W, 16¼" H



1668 BZ
1668 BZ-LED
6" W, 16¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
1668 BZ	2-20w GU10*	1668 BZ-LED	11w LED	900	2700K	96	1-35w, 1-50w	3½"	8¼"	4½" Square
1668 SK	2-20w GU10*	1668 SK-LED	11w LED	900	2700K	96	1-35w, 1-50w	3½"	8¼"	4½" Square
1668 TT	2-20w GU10*	1668 TT-LED	11w LED	900	2700K	96	1-35w, 1-50w	3½"	8¼"	4½" Square
1669 BZ	2-20w GU10*	1669 BZ-LED	11w LED	900	2700K	96	1-35w, 1-50w	4¾"	12"	6¾" W, 4½" H
1669 SK	2-20w GU10*	1669 SK-LED	11w LED	900	2700K	96	1-35w, 1-50w	4¾"	12"	6¾" W, 4½" H
1669 TT	2-20w GU10*	1669 TT-LED	11w LED	900	2700K	96	1-35w, 1-50w	4¾"	12"	6¾" W, 4½" H

*GU10 bulb included. For full product details and LED specifications, refer to hinkleylighting.com.



1664 SK
1664 SK-LED
9" W, 24" H



1664 TT
1664 TT-LED
9" W, 24" H



1664 BZ
1664 BZ-LED
9" W, 24" H



1660 SK
1660 SK-LED
6" W, 16" H



1660 TT
1660 TT-LED
6" W, 16" H



1660 BZ
1660 BZ-LED
6" W, 16" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
1660 BZ	2-20w GU-10*	1660 BZ-LED	15w LED	1200	2700K	96	2-50w	3½"	10" to 13½"***	6" W, 16" H
1660 SK	2-20w GU-10*	1660 SK-LED	15w LED	1200	2700K	96	2-50w	3½"	10" to 13½"***	6" W, 16" H
1660 TT	2-20w GU-10*	1660 TT-LED	15w LED	1200	2700K	96	2-50w	3½"	10" to 13½"***	6" W, 16" H
1664 BZ	2-20w GU-10*	1664 BZ-LED	15w LED	1200	2700K	96	2-50w	4"	11½" to 20½"***	9" W, 24" H
1664 SK	2-20w GU-10*	1664 SK-LED	15w LED	1200	2700K	96	2-50w	4"	11½" to 20½"***	9" W, 24" H
1664 TT	2-20w GU-10*	1664 TT-LED	15w LED	1200	2700K	96	2-50w	4"	11½" to 20½"***	9" W, 24" H

*GU-10 bulbs included. **Adjustable mounting hardware. For complete product details and LED specifications, refer to hinkleylighting.com.




1661 will cast light down



1662 will cast light up and down



POCKET DOWN LIGHT
1661 BZ
9" W, 5" H
Icons: Three dots, Moon, T24, Wheelchair




POCKET DOWN LIGHT
1661 TT
9" W, 5" H
Icons: Three dots, Moon, T24, Wheelchair



POCKET DOWN LIGHT
1661 SK
9" W, 5" H
Icons: Three dots, Moon, T24, Wheelchair



POCKET UP/DOWN LIGHT
1662 BZ
9" W, 5" H
Icons: T24, Wheelchair



POCKET UP/DOWN LIGHT
1662 TT
9" W, 5" H
Icons: Three dots, T24, Wheelchair



POCKET UP/DOWN LIGHT
1662 SK
9" W, 5" H
Icons: Three dots, T24, Wheelchair

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
1661 BZ	8w LED	600	2700K	96	1-50w	4"	2½"	9" W, 5" H
1661 SK	8w LED	600	2700K	96	1-50w	4"	2½"	9" W, 5" H
1661 TT	8w LED	600	2700K	96	1-50w	4"	2½"	9" W, 5" H
1662 BZ	15w LED	1200	2700K	96	2-50w	4"	2½"	9" W, 5" H
1662 SK	15w LED	1200	2700K	96	2-50w	4"	2½"	9" W, 5" H
1662 TT	15w LED	1200	2700K	96	2-50w	4"	2½"	9" W, 5" H

For complete product details and LED specifications, refer to hinkleylighting.com.



1647 BZ-LED

9" W, 9" H



1647 SW-LED

9" W, 9" H



1647 SK-LED

9" W, 9" H



1647 TT-LED

9" W, 9" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
1647 BZ-LED	15w LED	1200	2700K	96	2-50w	4"	4½"	4½" W, 6¾" H
1647 SK-LED	15w LED	1200	2700K	96	2-50w	4"	4½"	4½" W, 6¾" H
1647 SW-LED	15w LED	1200	2700K	96	2-50w	4"	4½"	4½" W, 6¾" H
1647 TT-LED	15w LED	1200	2700K	96	2-50w	4"	4½"	4½" W, 6¾" H

For full product details and LED specifications, refer to hinkleylighting.com.



CEILING MOUNT
1665 BZ
 8" DIA., 3¼" H



CEILING MOUNT
1665 TT
 8" DIA., 3¼" H



CEILING MOUNT
1665 SK
 8" DIA., 3¼" H



1659 SK
 9" W, 9" H



1659 TT
 9" W, 9" H



1659 BZ
 9" W, 9" H

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY
1659 BZ	15w LED	1200	2700K	96	2-50w	4"	4½"	9" Square Back Plate
1659 SK	15w LED	1200	2700K	96	2-50w	4"	4½"	9" Square Back Plate
1659 TT	15w LED	1200	2700K	96	2-50w	4"	4½"	9" Square Back Plate
1665 BZ	8w LED	600	2700K	96	1-50w			8" Dia. Canopy
1665 SK	8w LED	600	2700K	96	1-50w			8" Dia. Canopy
1665 TT	8w LED	600	2700K	96	1-50w			8" Dia. Canopy

For complete product details and LED specifications, refer to hinkleylighting.com.

KORE™

FINISH TITANIUM, BRONZE
GLASS ETCHED

Chic and minimal, Kore's contemporary aluminum form is offered in either sleek square or round sconces with etched glass lenses. Modern finish options and the option of selecting light to emanate from both up and down or down only complete its bold yet streamlined appearance.

 exclusively available in
HIGH-PERFORMANCE LED



1873 + 1877 will
cast light down



1873 BZ
5¼" W, 7½" H



1873 TT
5¼" W, 7½" H



1877 BZ
5¼" W, 7½" H



1877 TT
5¼" W, 7½" H





1872 + 1876 will cast light up and down



1876 TT
5¼" W, 7½" H



1876 BZ
5¼" W, 7½" H



1872 TT
5¼" W, 7½" H



1872 BZ
5¼" W, 7½" H



LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
1872 BZ	8w LED	600	3000K	80	2-35w	4"	3¾"	5¼" Square
1872 TT	8w LED	600	3000K	80	2-35w	4"	3¾"	5¼" Square
1873 BZ	5w LED	300	3000K	80	1-35w	4"	3¾"	5¼" Square
1873 TT	5w LED	300	3000K	80	1-35w	4"	3¾"	5¼" Square
1876 BZ	8w LED	600	3000K	80	2-35w	4"	3¾"	5¼" Square
1876 TT	8w LED	600	3000K	80	2-35w	4"	3¾"	5¼" Square
1877 BZ	5w LED	300	3000K	80	1-35w	4"	3¾"	5¼" Square
1877 TT	5w LED	300	3000K	80	1-35w	4"	3¾"	5¼" Square

For full product details and LED specifications, refer to hinkleylighting.com.

CASCADE™

FINISH BRONZE, SATIN
BLACK, TITANIUM
GLASS CLEAR ETCHED
ORGANIC RAIN, AMBER
ETCHED ORGANIC RAIN

The clean, modern lines of Cascade complement the rain glass while creating a glowing, indirect lighting effect. The sleek aluminum construction adds to the design's versatility, making this contemporary style perfect for either interior or exterior use. Cascade is standard Dark Sky compliant.



1830 BZ
1830 BZ-LED
8" W, 14½" H



1830 TT
1830 TT-LED
8" W, 14½" H



1830 SK
1830 SK-LED
8" W, 14½" H



1834 BZ
1834 BZ-LED
8" W, 18" H



1834 TT
1834 TT-LED
8" W, 18" H



1834 SK
1834 SK-LED
8" W, 18" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
1830 BZ	1-100w Med.	1830 BZ-LED	15w LED	800	2700K	96	1-100w	4"	4¾"	8" W, 14½" H
1830 SK	1-100w Med.	1830 SK-LED	15w LED	800	2700K	96	1-100w	4"	4¾"	8" W, 14½" H
1830 TT	1-100w Med.	1830 TT-LED	15w LED	800	2700K	96	1-100w	4"	4¾"	8" W, 14½" H
1834 BZ	1-100w Med.	1834 BZ-LED	15w LED	800	2700K	96	1-100w	4"	4¾"	8" W, 18" H
1834 SK	1-100w Med.	1834 SK-LED	15w LED	800	2700K	96	1-100w	4"	4¾"	8" W, 18" H
1834 TT	1-100w Med.	1834 TT-LED	15w LED	800	2700K	96	1-100w	4"	4¾"	8" W, 18" H

For complete product details and LED specifications, refer to hinkleylighting.com.

Titan's sleek design in solid aluminum features organic ribbed etched glass that creates an indirect wall wash for a sophisticated appearance.



FINISH BUCKEYE BRONZE, TITANIUM
GLASS ORGANIC RIBBED ETCHED



TITAN™



2050 KZ
2050 KZ-LED
6¾" W, 14" H
 

2054 KZ
2054 KZ-LED
8½" W, 17½" H
 

2050 TT
2050 TT-LED
6¾" W, 14" H
 

2054 TT
2054 TT-LED
8½" W, 17½" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
2050 KZ	1-100w Med.	2050 KZ-LED	8.5w LED	600	3000K	96	1-60w	4½"	7"	6¾" W, 14" H
2050 TT	1-100w Med.	2050 TT-LED	8.5w LED	600	3000K	96	1-60w	4½"	7"	6¾" W, 14" H
2054 KZ	1-100w Med.	2054 KZ-LED	17w LED	1200	3000K	96	1-100w	4¾"	8¾"	8½" W, 17½" H
2054 TT	1-100w Med.	2054 TT-LED	17w LED	1200	3000K	96	1-100w	4¾"	8¾"	8½" W, 17½" H

For complete product details and LED specifications, refer to hinkleylighting.com.

ATLANTIS™


FINISH SATIN BLACK
GLASS ETCHED GLASS LENS

Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.

ADDITIONAL FINISHES

Bronze (BZ), Satin White (SW), Titanium (TT)

INSTAFAVE



@cueto_interiors

THE ATLANTIS COLLECTION



1639 SK
1639 SK-LED
12" W, 36" H





1646 (left) will cast light down

1645 (right) will cast light up and down



POCKET DOWN LIGHT
1646 SK
1646 SK-LED
9" W, 6" H



POCKET UP/DOWN LIGHT
1645 SK
1645 SK-LED
9" W, 6" H



1648 SK
1648 SK-LED
6" W, 16" H



1640 SK
1640 SK-LED
2¾" W, 16" H



1644 SK
1644 SK-LED
3" W, 24" H



1649 SK
1649 SK-LED
9" W, 24" H



1641 SK
1641 SK-LED
6¾" W, 24½" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE
1639 SK	3-50w GU-10*	1639 SK-LED	23w LED	1800	2700K	96	3-50w	4"		31"	4½" W, 6¾" H
1640 SK	2-20w MR-16**	1640 SK-LED	11w LED	900	2700K	96	1-35w, 1-50w	6½"		8"	4½" Square
1641 SK	2-20w MR-16**	1641 SK-LED	11w LED	900	2700K	96	1-35w, 1-50w		3"		3" Dia. Post Fitter
1644 SK	2-20w MR-16**	1644 SK-LED	11w LED	900	2700K	96	1-35w, 1-50w	7½"		12"	4½" Square
1645 SK	1-75w Med.	1645 SK-LED	15w LED	1200	2700K	96	2-50w	4¼"		3"	4½" Square
1646 SK	1-75w Med.	1646 SK-LED	7.5w LED	600	2700K	96	1-50w	4¼"		3"	4½" Square
1648 SK	2-20w MR-16**	1648 SK-LED	11w LED	900	2700K	96	1-35w, 1-50w	3½"		13¾"	4½" Square
1649 SK	2-20w GU-10*	1649 SK-LED	11w LED	900	2700K	96	1-35w, 1-50w	4"		20¾"	4½" W, 6¾" H

*GU-10 bulb included. **MR-16 bulbs included. For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.


ATLANTIS™

FINISH TITANIUM
GLASS CASED OPAL OR
ETCHED GLASS LENS

Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.

ADDITIONAL FINISHES

Bronze (BZ), Satin Black (SK), Satin White (SW)



1639 TT
1639 TT-LED
12" W, 36" H





1646 (left) will cast light down

1645 (right) will cast light up and down



1650 TT
1650 TT-LED
6½" W, 10½" H
T24



POCKET DOWN LIGHT
1646 TT
1646 TT-LED
9" W, 6" H
T24



POCKET UP/DOWN LIGHT
1645 TT
1645 TT-LED
9" W, 6" H
T24



1648 TT
1648 TT-LED
6" W, 16" H
T24



1640 TT
1640 TT-LED
2¾" W, 16" H
T24



1655 TT
1655 TT-LED
9" W, 15½" H
T24



1644 TT
1644 TT-LED
3" W, 24" H
T24



1649 TT
1649 TT-LED
9" W, 24" H
T24



1641 TT
1641 TT-LED
6¾" W, 24½" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE
1639 TT	3-50w GU-10*	1639 TT-LED	23w LED	1800	2700K	96	3-50w	4"		31"	4½" W, 6¾" H
1640 TT	2-20w MR-16**	1640 TT-LED	11w LED	900	2700K	96	1-35w, 1-50w	6½"		8"	4½" Square
1641 TT	2-20w MR-16**	1641 TT-LED	11w LED	900	2700K	96	1-35w, 1-50w		3"		3" Dia. Post Fitter
1644 TT	2-20w MR-16**	1644 TT-LED	11w LED	900	2700K	96	1-35w, 1-50w	7½"		12"	4½" Square
1645 TT	1-75w Med.	1645 TT-LED	15w LED	1200	2700K	96	2-50w	4¼"		3"	4½" Square
1646 TT	1-75w Med.	1646 TT-LED	7.5w LED	600	2700K	96	1-50w	4¼"		3"	4½" Square
1648 TT	2-20w MR-16**	1648 TT-LED	11w LED	900	2700K	96	1-35w, 1-50w	3½"		13¾"	4½" Square
1649 TT	2-20w GU-10*	1649 TT-LED	11w LED	900	2700K	96	1-35w, 1-50w	4"		20¾"	4½" W, 6¾" H
1650 TT	1-60w Med.	1650 TT-LED	8.5w LED	600	3000K	96	1-60w	4"		5¼"	5½" W, 4½" H
1655 TT	1-100w Med.	1655 TT-LED	17w LED	1200	3000K	96	1-100w	5¾"		7¾"	5½" W, 7" H

*GU-10 bulb included. **MR-16 bulbs included. For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

ATLANTIS™

FINISH BRONZE
GLASS CASED OPAL OR
ETCHED GLASS LENS

Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.

ADDITIONAL FINISHES

Satin Black (SK), Satin White (SW), Titanium (TT)

— @INSTAFAVE —



@melissamorgandesign
THE ATLANTIS COLLECTION



1639 BZ
1639 BZ-LED
12" W, 36" H





1646 (left) will cast light down

1645 (right) will cast light up and down



1650 BZ
1650 BZ-LED
6½" W, 10½" H
T24 ♿



POCKET DOWN LIGHT
1646 BZ
1646 BZ-LED
9" W, 6" H
T24 ♿



POCKET UP/DOWN LIGHT
1645 BZ
1645 BZ-LED
9" W, 6" H
T24 ♿



1648 BZ
1648 BZ-LED
6" W, 16" H
T24 ♿



1640 BZ
1640 BZ-LED
2¾" W, 16" H
T24 ♿



1655 BZ
1655 BZ-LED
9" W, 15½" H
T24 ♿



1644 BZ
1644 BZ-LED
3" W, 24" H
T24 ♿



1649 BZ
1649 BZ-LED
9" W, 24" H
T24 ♿



1641 BZ
1641 BZ-LED
6¾" W, 24½" H
T24 ♿

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE
1639 BZ	3-50w GU-10*	1639 BZ-LED	23w LED	1800	2700K	96	3-50w	4"		31"	4½" W, 6¾" H
1640 BZ	2-20w MR-16**	1640 BZ-LED	11w LED	900	2700K	96	1-35w, 1-50w	6½"		8"	4½" Square
1641 BZ	2-20w MR-16**	1641 BZ-LED	11w LED	900	2700K	96	1-35w, 1-50w		3"		3" Dia. Post Fitter
1644 BZ	2-20w MR-16**	1644 BZ-LED	11w LED	900	2700K	96	1-35w, 1-50w	7½"		12"	4½" Square
1645 BZ	1-75w Med.	1645 BZ-LED	15w LED	1200	2700K	96	2-50w	4¼"		3"	4½" Square
1646 BZ	1-75w Med.	1646 BZ-LED	7.5w LED	600	2700K	96	1-50w	4¼"		3"	4½" Square
1648 BZ	2-20w MR-16**	1648 BZ-LED	11w LED	900	2700K	96	1-35w, 1-50w	3½"		13¾"	4½" Square
1649 BZ	2-20w GU-10*	1649 BZ-LED	11w LED	900	2700K	96	1-35w, 1-50w	4"		20¾"	4½" W, 6¾" H
1650 BZ	1-60w Med.	1650 BZ-LED	8.5w LED	600	3000K	96	1-60w	4"		5¼"	5½" W, 4½" H
1655 BZ	1-100w Med.	1655 BZ-LED	17w LED	1200	3000K	96	1-100w	5¾"		7¾"	5½" W, 7" H

*GU-10 bulb included. **MR-16 bulbs included. For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

ATLANTIS™

FINISH SATIN WHITE
GLASS ETCHED GLASS LENS

Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.

ADDITIONAL FINISHES

Bronze (BZ), Satin Black (SK), Titanium (TT)



1646 will cast light down



1645 will cast light up and down



POCKET DOWN LIGHT

1646 SW
1646 SW-LED
9" W, 6" H



POCKET UP/DOWN LIGHT

1645 SW
1645 SW-LED
9" W, 6" H



1640 SW
1640 SW-LED
2 3/4" W, 16" H



1648 SW
1648 SW-LED
6" W, 16" H



1649 SW
1649 SW-LED
9" W, 24" H



1644 SW
1644 SW-LED
3" W, 24" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
1640 SW	2-20w MR-16**	1640 SW-LED	11w LED	900	2700K	96	1-35w, 1-50w	6 3/4"	8"	4 1/2" Square
1644 SW	2-20w MR-16**	1644 SW-LED	11w LED	900	2700K	96	1-35w, 1-50w	7 1/2"	12"	4 1/2" Square
1645 SW	1-75w Med.	1645 SW-LED	15w LED	1200	2700K	96	2-50w	4 1/4"	2 3/4"	4 1/2" Square
1646 SW	1-75w Med.	1646 SW-LED	7.5w LED	600	2700K	96	1-50w	4 1/4"	2 3/4"	4 1/2" Square
1648 SW	2-20w MR-16**	1648 SW-LED	11w LED	900	2700K	96	1-35w, 1-50w	3 1/2"	13 3/4"	4 1/2" Square
1649 SW	2-20w GU-10*	1649 SW-LED	11w LED	900	2700K	96	1-35w, 1-50w	4"	20 3/4"	4 1/2" W, 6 3/4" H

*GU-10 bulb included. **MR-16 bulbs included. For full product details and LED specifications, refer to hinkleylighting.com.

A collection of sleek designs, Kube's contemporary style featuring solid aluminum construction provides a chic, minimalist statement to complement a variety of exteriors.

FINISH BRONZE, TITANIUM,
SATIN BLACK, SATIN WHITE
GLASS ETCHED LENS

KUBE™



1768 (left) will cast light down

1769 (right) will cast light up and down

exclusively available in  HIGH-PERFORMANCE LED



CEILING MOUNT
1765 BZ
6" W, 3½" H
  



CEILING MOUNT
1765 TT
6" W, 3½" H
  



CEILING MOUNT
1765 SK
6" W, 3½" H
  



CEILING MOUNT
1765 SW
6" W, 3½" H
  



POCKET DOWN LIGHT
1768 BZ
6" W, 6" H
  



POCKET DOWN LIGHT
1768 TT
6" W, 6" H
  



POCKET DOWN LIGHT
1768 SK
6" W, 6" H
  



POCKET DOWN LIGHT
1768 SW
6" W, 6" H
  





POCKET UP/DOWN LIGHT
1769 BZ
6" W, 6" H
 



POCKET UP/DOWN LIGHT
1769 TT
6" W, 6" H
 



POCKET UP/DOWN LIGHT
1769 SK
6" W, 6" H
 



POCKET UP/DOWN LIGHT
1769 SW
6" W, 6" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY
1765 BZ, SK, SW, TT	8w LED	600	2700K	96	1-50w			6" Square Canopy
1768 BZ, SK, SW, TT	8w LED	600	2700K	96	1-50w	6¾"	3"	4½" Square Back Plate
1769 BZ, SK, SW, TT	15w LED	1200	2700K	96	2-50w	6¾"	3"	4½" Square Back Plate

For full product details and LED specifications, refer to hinkleylighting.com.

DORIAN™

FINISH TITANIUM
GLASS CLEAR PAINTED WHITE INSIDE

Dorian's robust design in durable aluminum construction is offered in either Titanium or Bronze finishes. This contemporary fixture allows light to emit from white etched glass windows.

ADDITIONAL FINISHES
Bronze (BZ)



2198 TT
6" W, 36" H





2194 TT
2194 TT-LED
6" W, 18¼" H
T24

2190 TT
2190 TT-LED
6" W, 12¼" H
T24

2192 TT
2192 TT-LED
6" W, 18¼" H
T24

2195 TT
2195 TT-LED
6" W, 24¼" H
T24

2191 TT
2191 TT-LED
6" W, 20¾" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE
2190 TT	1-100w Med.	2190 TT-LED	15w LED	1200	3000K	96	1-100w	6¾"	6¼"	4½" Square Back Plate	
2191 TT	1-100w Med.	2191 TT-LED	30w LED	2400	3000K	96	2-100w			3" Dia. Post Fitter	
2192 TT	1-100w Med.	2192 TT-LED	30w LED	2400	3000K	96	2-100w			5" Dia. Canopy	6'
2194 TT	1-100w Med.	2194 TT-LED	15w LED	1200	3000K	96	1-100w	6¾"	9¼"	4½" Square Back Plate	
2195 TT	2-100w Med.	2195 TT-LED	23w LED	1800	3000K	96	2-75w	6¾"	12¼"	4½" Square Back Plate	
		2198 TT	37w LED	3600	3000K	96	4-75w	6¾"	18"	6" W, 10" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

DORIAN™


FINISH BRONZE
GLASS CLEAR PAINTED WHITE INSIDE

Dorian's robust design in durable aluminum construction is offered in either Titanium or Bronze finishes. This contemporary fixture allows light to emit from white etched glass windows.

ADDITIONAL FINISHES
Titanium (TT)



2198 BZ
6" W, 36" H
 



2192 BZ
2192 BZ-LED
6" W, 18¼" H
T24



2194 BZ
2194 BZ-LED
6" W, 18¼" H
T24



2190 BZ
2190 BZ-LED
6" W, 12¼" H
T24



2195 BZ
2195 BZ-LED
6" W, 24¼" H
T24



2191 BZ
2191 BZ-LED
6" W, 20¾" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE
2190 BZ	1-100w Med.	2190 BZ-LED	15w LED	1200	3000K	96	1-100w	6¾"	6¼"	4½" Square Back Plate	
2191 BZ	1-100w Med.	2191 BZ-LED	30w LED	2400	3000K	96	2-100w			3" Dia. Post Fitter	
2192 BZ	1-100w Med.	2192 BZ-LED	30w LED	2400	3000K	96	2-100w			5" Dia. Canopy	6'
2194 BZ	1-100w Med.	2194 BZ-LED	15w LED	1200	3000K	96	1-100w	6¾"	9¼"	4½" Square Back Plate	
2195 BZ	2-100w Med.	2195 BZ-LED	23w LED	1800	3000K	96	2-75w	6¾"	12¼"	4½" Square Back Plate	
		2198 BZ	37w LED	3600	3000K	96	4-75w	6¾"	18"	6" W, 10" H Back Plate	


For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

ARIA™

FINISH BLACK

Aria is a contemporary style that effortlessly complements the facade of any exterior. Its modern shape in durable aluminum is enhanced by a stainless steel mesh shade. Aria's high style and low maintenance comes standard Dark Sky compliant.

ADDITIONAL FINISHES
Buckeye Bronze (KZ)



2305 BK
2305 BK-LED
7 1/4" W, 21 3/4" H





2302 BK
2302 BK-LED
5¼" W, 15¾" H
48" MAX. H*






2300 BK
2300 BK-LED
5¼" W, 15½" H






2306 BK
2306 BK-LL
4½" W, 14½" H





2304 BK
2304 BK-LED
5¼" W, 18½" H






2307 BK
2307 BK-LL
7½" W, 17¼" H






2307 BK
2307 BK-LL
(side view)
7½" W, 17¼" H




ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2300 BK	1-75w Med.	2300 BK-LED	15w LED	1100	2700K	92	1-75w	6¾"	5"	4½" W, 8¼" H Back Plate		
2302 BK	1-100w Med.	2302 BK-LED	15w LED	1100	2700K	92	1-75w			6" Dia. Canopy	10'	1-6", 2-12"
2304 BK	1-100w Med.	2304 BK-LED	15w LED	1100	2700K	92	1-75w	6¾"	5"	4½" W, 8¼" H Back Plate		
2305 BK	1-100w Med.	2305 BK-LED	15w LED	1100	2700K	92	1-75w	8¾"	5"	4½" W, 8¼" H Back Plate		
2306 BK	1-50w GU-10**	2306 BK-LL	1-6.5w GU10 LED***					4¾"	5"	4½" W, 8¼" H Back Plate		
2307 BK	1-50w GU-10**	2307 BK-LL	1-6.5w GU10 LED***					4"	2½"	7½" W, 4¾" H Back Plate		

Reflector type or Par type lamp recommended. *Maximum achievable height with stems included. Additional stems available, 6034 BKOD. **GU10 bulb included. ***GU10 LED bulb included. For full product details and LED specifications, refer to hinkleylighting.com.

ARIA™

FINISH BUCKEYE BRONZE

Aria is a contemporary style that effortlessly complements the facade of any exterior. Its modern shape in durable aluminum is enhanced by a stainless steel mesh shade. Aria's high style and low maintenance comes standard Dark Sky compliant.

ADDITIONAL FINISHES
Black (BK)



2305 KZ
2305 KZ-LED
7¼" W, 21¾" H





2302 KZ
2302 KZ-LED
5¼" W, 15¾" H
48" MAX. H*
  



2300 KZ
2300 KZ-LED
5¼" W, 15½" H
  




2306 KZ
2306 KZ-LL
4½" W, 14½" H
 



2304 KZ
2304 KZ-LED
5¼" W, 18½" H
  



2307 KZ
2307 KZ-LL
7½" W, 17¼" H
 



2307 KZ
2307 KZ-LL
(side view)
7½" W, 17¼" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2300 KZ	1-75w Med.	2300 KZ-LED	15w LED	1100	2700K	92	1-75w	6¾"	5"	4½" W, 8¼" H Back Plate		
2302 KZ	1-100w Med.	2302 KZ-LED	15w LED	1100	2700K	92	1-75w			6" Dia. Canopy	10'	1-6", 2-12"
2304 KZ	1-100w Med.	2304 KZ-LED	15w LED	1100	2700K	92	1-75w	6¾"	5"	4½" W, 8¼" H Back Plate		
2305 KZ	1-100w Med.	2305 KZ-LED	15w LED	1100	2700K	92	1-75w	8¾"	5"	4½" W, 8¼" H Back Plate		
2306 KZ	1-50w GU-10**	2306 KZ-LL	1-6.5w GU10 LED***					4¾"	5"	4½" W, 8¼" H Back Plate		
2307 KZ	1-50w GU-10**	2307 KZ-LL	1-6.5w GU10 LED***					4"	2½"	7½" W, 4¾" H Back Plate		

Reflector type or Par type lamp recommended. *Maximum achievable height with stems included. Additional stems available, 6034 KZOD. **GU10 bulb included. ***GU10 LED bulb included. For full product details and LED specifications, refer to hinkleylighting.com.

SHELTER™

FINISH BLACK
GLASS CLEAR SEEDY

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.

ADDITIONAL FINISHES

Hematite (HE), Buckeye Bronze (KZ)



1325 BK
1325 BK-LED
8¼" W, 23¼" H
Icons: Recycle, Dark Sky, T24



1326 BK
1326 BK-LL
4½" W, 15½" H
Icons: Recycle, Dark Sky



1320 BK
1320 BK-LED
6¼" W, 15½" H
Icons: Recycle, Dark Sky, T24



1324 BK
1324 BK-LED
6¼" W, 20½" H
Icons: Recycle, Dark Sky, T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
1320 BK	1-75w Med.	1320 BK-LED	10w LED	550	2700K	96	1-60w	6½"	4¾"	4½" W, 12" H
1324 BK	1-100w Med.	1324 BK-LED	15w LED	1100	2700K	92	1-75w	6½"	5¾"	4½" W, 12" H
1325 BK	1-100w Med.	1325 BK-LED	15w LED	1100	2700K	92	1-75w	8½"	5¾"	4½" W, 12" H
1326 BK	1-50w GU-10*	1326 BK-LL	1-6.5w GU10 LED**					4¾"	5¾"	4½" W, 12" H

*GU10 bulb included. **GU10 LED bulb included. For full product details and LED specifications, refer to hinkleylighting.com.



1328 BK
1328 BK-LED
8¼" DIA., 24½" H
57" MAX. H*



1322 BK
1322 BK-LED
6¼" DIA., 21¾" H
54¼" MAX. H*



1344 BK
8½" W, 18" H



1340 BK
6" W, 13" H



1321 BK
1321 BK-LED
(shown as pier mount
with 1304 BK)**
8¼" DIA., 27¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
1321 BK	1-100w Med.	1321 BK-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter		
1322 BK	1-100w Med.	1322 BK-LED	15w LED	1100	2700K	92	1-75w			6" Dia. Canopy	10'	1-6", 2-12"
1328 BK	1-100w Med.	1328 BK-LED	15w LED	1100	2700K	92	1-75w			6" Dia. Canopy	10'	1-6", 2-12"
		1340 BK	16w LED	900	2700K	90	1-75w	3¾"	2½"	5½" W, 4¾" H Back Plate		
		1344 BK	16w LED	900	2700K	90	1-75w	4"	3"	7¾" W, 5¼" H Back Plate		

*Maximum achievable height with stems included. Additional stems available, 6034 BKOD. For full product details and LED specifications, refer to hinkleylighting.com. **Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

SHELTER™

FINISH BUCKEYE BRONZE
GLASS CLEAR SEEDY

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.

ADDITIONAL FINISHES
Black (BK), Hematite (HE)



1325 KZ
1325 KZ-LED
8¼" W, 23¼" H




1320 KZ
1320 KZ-LED
6¼" W, 15½" H




1324 KZ
1324 KZ-LED
6¼" W, 20½" H


ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
1320 KZ	1-75w Med.	1320 KZ-LED	10w LED	550	2700K	96	1-60w	6½"	4¾"	4½" W, 12" H
1324 KZ	1-100w Med.	1324 KZ-LED	15w LED	1100	2700K	92	1-75w	6½"	5¾"	4½" W, 12" H
1325 KZ	1-100w Med.	1325 KZ-LED	15w LED	1100	2700K	92	1-75w	8½"	5¾"	4½" W, 12" H

For full product details and LED specifications, refer to hinkleylighting.com.



1322 KZ
1322 KZ-LED
6¼" DIA., 21¾" H
54¼" MAX. H*







1321 KZ
1321 KZ-LED
8¼" DIA., 27¾" H







1326 KZ
1326 KZ-LL
4½" W, 15½" H






1344 KZ
8½" W, 18" H








1340 KZ
6" W, 13" H






ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
1321 KZ	1-100w Med.	1321 KZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter		
1322 KZ	1-100w Med.	1322 KZ-LED	15w LED	1100	2700K	92	1-75w			6" Dia. Canopy	10'	1-6", 2-12"
1326 KZ	1-50w GU-10**	1326 KZ-LL	1-6.5w GU10 LED***					4¾"	5¾"	4½" W, 12" H Back Plate		
		1340 KZ	16w LED	900	2700K	90	1-75w	3¾"	2½"	5½" W, 4¾" H Back Plate		
		1344 KZ	16w LED	900	2700K	90	1-75w	4"	3"	7¾" W, 5¼" H Back Plate		

*Maximum achievable height with stems included. Additional stems available, 6034 KZOD. **GU10 bulb included. ***GU10 LED bulb included. For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

SHELTER™

FINISH HEMATITE
GLASS CLEAR SEEDY

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the light from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.

ADDITIONAL FINISHES

Black (BK), Buckeye Bronze (KZ)



1325 HE
1325 HE-LED
8¼" W, 23¼" H



1320 HE
1320 HE-LED
6¼" W, 15½" H




1324 HE
1324 HE-LED
6¼" W, 20½" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
1320 HE	1-75w Med.	1320 HE-LED	10w LED	550	2700K	96	1-60w	6½"	4¾"	4½" W, 12" H
1324 HE	1-100w Med.	1324 HE-LED	15w LED	1100	2700K	92	1-75w	6½"	5¾"	4½" W, 12" H
1325 HE	1-100w Med.	1325 HE-LED	15w LED	1100	2700K	92	1-75w	8½"	5¾"	4½" W, 12" H

For full product details and LED specifications, refer to hinkleylighting.com.



1322 HE
1322 HE-LED
6¼" DIA., 21¾" H
54¼" MAX. H*



1321 HE
1321 HE-LED
8¼" DIA., 27¾" H



1326 HE
1326 HE-LL
4½" W, 15½" H



1344 HE
8½" W, 18" H



1340 HE
6" W, 13" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
1321 HE	1-100w Med.	1321 HE-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter		
1322 HE	1-100w Med.	1322 HE-LED	15w LED	1100	2700K	92	1-75w			6" Dia. Canopy	10'	1-6", 2-12"
1326 HE	1-50w GU-10**	1326 HE-LL	1-6.5w GU10 LED***					4¾"	5¾"	4½" W, 12" H Back Plate		
		1340 HE	16w LED	900	2700K	90	1-75w	3¾"	2½"	5½" W, 4¾" H Back Plate		
		1344 HE	16w LED	900	2700K	90	1-75w	4"	3"	7¾" W, 5¼" H Back Plate		

*Maximum achievable height with stems included. Additional stems available, 6034 HEOD. **GU10 bulb included. ***GU10 LED bulb included. For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

HORIZON™

FINISH BLACK,
BUCKEYE BRONZE
GLASS CLEAR SEEDY

Horizon's simple elegance emphasizes its dominant expanse of clear seedy glass finished with a flame polished edge. This versatile fixture is constructed of die-cast aluminum and can be mounted horizontally, vertically or on the ceiling. The center band, available in either Buckeye Bronze or Black finish options, is uniquely adjustable to allow flexible mounting options. The open top and bottom maximizes the output of the dimmable LED light source.



exclusively available in
HIGH-PERFORMANCE LED



2895 BK
5¼" W, 20½" H



2895 KZ
5¼" W, 20½" H






2894 BK
5¼" W, 17" H



2894 KZ
5¼" W, 17" H



@dhillon_lighting_yyc
THE HORIZON COLLECTION



2890 KZ
(mounted horizontally)



2890 BK
5¼" W, 12" H



2890 KZ
(side view)
5¼" W, 12" H

DESIGN NOTE



Horizon's adjustable mounting allows you to choose your glass position creating multiple looks with one fixture.*

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE
2890 BK	16w LED	800	2700K	91	1-75w	3¾"	4½", 6¼", 7¾"	5" W, 4½" H
2890 KZ	16w LED	800	2700K	91	1-75w	3¾"	4½", 6¼", 7¾"	5" W, 4½" H
2894 BK	16w LED	800	2700K	91	1-75w	3¾"	5¾", 8½", 11½"	5" W, 4½" H
2894 KZ	16w LED	800	2700K	91	1-75w	3¾"	5¾", 8½", 11½"	5" W, 4½" H
2895 BK	16w LED	800	2700K	91	1-75w	3¾"	7½", 10¼", 13¼"	5" W, 4½" H
2895 KZ	16w LED	800	2700K	91	1-75w	3¾"	7½", 10¼", 13¼"	5" W, 4½" H

*Multiple top to outlet measurements with adjustable glass positioning. For full product details and LED specifications, refer to hinkleylighting.com.

SATURN™

FINISH SATIN BLACK
GLASS CLEAR SEEDY

Saturn is a stunning, modern design in Satin Black, offering robust construction and intersecting lines that create a striking contrast against the clear seedy glass.

ADDITIONAL FINISHES

Metro Bronze (MT), Stainless Steel (SS)



POCKET WALL MOUNT
1909 SK
8" W, 20½" H



1902 SK
10" DIA., 21¼" H



1904 SK
8" W, 16" H



POCKET WALL MOUNT
1908 SK
7¼" W, 12½" H




1900 SK
6" W, 12" H



1905 SK
10" W, 20¼" H



1901 SK
10" DIA., 21¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1900 SK	1-60w Med.	7½"	7½"	4¾" W, 9" H Back Plate	
1901 SK	1-100w Med.			3" Dia. Post Fitter	
1902 SK	1-100w Med.			5" Dia. Canopy	6', 5'
1904 SK	1-75w Med.	9½"	9"	4¾" W, 14" H Back Plate	
1905 SK	1-100w Med.	11½"	13"	4¾" W, 14" H Back Plate	
1908 SK	2-40w Cand.	4"	6¼"	5¾" W, 12½" H Back Plate	
1909 SK	2-75w Med.	4½"	10½"	5¼" W, 20" H Back Plate	

For posts and pier mounts, see pages 664-665.

SATURN™

FINISH METRO BRONZE
GLASS ETCHED OPAL

Saturn is a stunning, modern design in Metro Bronze, offering robust construction and intersecting lines that create a striking contrast against the etched opal glass.

ADDITIONAL FINISHES

Satin Black (SK), Stainless Steel (SS)



POCKET WALL MOUNT

1909 MT

1909 MT-LED

8" W, 20½" H








1902 MT
1902 MT-LED
10" DIA., 21¼" H
 



1904 MT
1904 MT-LED
8" W, 16" H
 



POCKET WALL MOUNT
1908 MT
1908 MT-LED
7¼" W, 12½" H
  





1900 MT
1900 MT-LED
6" W, 12" H
 



1905 MT
1905 MT-LED
10" W, 20¼" H
 



1901 MT
1901 MT-LED
10" DIA., 21¼" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1900 MT	1-60w Med.	1900 MT-LED	15w LED	1100	3000K	92	1-75w	7½"	7½"	4¾" W, 9" H Back Plate	
1901 MT	1-100w Med.	1901 MT-LED	30w LED	2400	3000K	96	2-100w			3" Dia. Post Fitter	
1902 MT	1-100w Med.	1902 MT-LED	30w LED	2400	3000K	96	2-100w			5" Dia. Canopy	6', 5'
1904 MT	1-75w Med.	1904 MT-LED	30w LED	2400	3000K	96	2-100w	9½"	9"	4¾" W, 14" H Back Plate	
1905 MT	1-100w Med.	1905 MT-LED	30w LED	2400	3000K	96	2-100w	11½"	13"	4¾" W, 14" H Back Plate	
1908 MT	2-40w Cand.	1908 MT-LED	15w LED	1200	3000K	96	1-100w	4"	6¼"	5¾" W, 12½" H Back Plate	
1909 MT	2-75w Med.	1909 MT-LED	23w LED	1800	3000K	96	2-75w	4½"	10½"	5¼" W, 20" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

SATURN™

FINISH STAINLESS STEEL
GLASS ETCHED OPAL

Saturn is a stunning, modern design in Stainless Steel, offering robust construction and intersecting lines that create a striking contrast against the etched opal glass.

ADDITIONAL FINISHES

Metro Bronze (MT), Satin Black (SK)





POCKET WALL MOUNT

1909 SS
1909 SS-LED
8" W, 20½" H








1902 SS
1902 SS-LED
10" DIA., 21¼" H
 





1904 SS
1904 SS-LED
8" W, 16" H
 




POCKET WALL MOUNT
1908 SS
1908 SS-LED
7¼" W, 12½" H
  





1900 SS
1900 SS-LED
6" W, 12" H
 



1905 SS
1905 SS-LED
10" W, 20¼" H
 



1901 SS
1901 SS-LED
10" DIA., 21¼" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1900 SS	1-60w Med.	1900 SS-LED	15w LED	1100	3000K	92	1-75w	7½"	7½"	4¾" W, 9" H Back Plate	
1901 SS	1-100w Med.	1901 SS-LED	30w LED	2400	3000K	96	2-100w			3" Dia. Post Fitter	
1902 SS	1-100w Med.	1902 SS-LED	30w LED	2400	3000K	96	2-100w			5" Dia. Canopy	6', 5'
1904 SS	1-75w Med.	1904 SS-LED	30w LED	2400	3000K	96	2-100w	9½"	9"	4¾" W, 14" H Back Plate	
1905 SS	1-100w Med.	1905 SS-LED	30w LED	2400	3000K	96	2-100w	11½"	13"	4¾" W, 14" H Back Plate	
1908 SS	2-40w Cand.	1908 SS-LED	15w LED	1200	3000K	96	1-100w	4"	6¼"	5¾" W, 12½" H Back Plate	
1909 SS	2-75w Med.	1909 SS-LED	23w LED	1800	3000K	96	2-75w	4½"	10½"	5¼" W, 20" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

COLFAX™

FINISH POLISHED STAINLESS STEEL
GLASS ETCHED OPAL

The sleek lines of Colfax feature intersecting planes of stainless steel and a chic cylinder of etched opal glass to create a sophisticated geometric form. The stainless steel construction in a Polished Stainless Steel finish brings an Arts & Crafts flair to the transitional design.

ADDITIONAL FINISHES Bronze (BZ)



2925 PS
9½" W, 19¼" H



2920 PS
6" W, 12¼" H



2924 PS
7½" W, 15¼" H



2922 PS
9½" W, 18¾" H,
60¼" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2920 PS	1-100w Med.	6¾"	4¼"	4½" W, 8¼" H Back Plate		
2922 PS	1-100w Med.			5" Dia. Canopy	10'	2-6", 2-12"
2924 PS	1-100w Med.	8¼"	4¼"	4½" W, 8¼" H Back Plate		
2925 PS	1-100w Med.	10½"	5¼"	5¾" W, 10½" H Back Plate		

*Maximum achievable height with stems included. Additional stems available, 6032 PS.

The sleek lines of Colfax feature intersecting planes of solid aluminum and a chic cylinder of etched opal glass to create a sophisticated geometric form. The die cast aluminum construction in a Bronze finish brings an Arts & Crafts flair to the transitional design.

FINISH BRONZE
GLASS ETCHED OPAL

COLFAX™

ADDITIONAL FINISHES
Polished Stainless Steel (PS)



2922 BZ
2922 BZ-LED
9½" W, 18¾" H,
60¼" MAX. H*



2920 BZ
2920 BZ-LED
6" W, 12¼" H



2924 BZ
2924 BZ-LED
7½" W, 15¼" H



2925 BZ
2925 BZ-LED
9½" W, 19¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2920 BZ	1-100w Med.	2920 BZ-LED	15w LED	1100	2700K	92	1-75w	6¾"	4¼"	4½" W, 8¼" H Back Plate		
2922 BZ	1-100w Med.	2922 BZ-LED	15w LED	1100	2700K	92	1-75w			5" Dia. Canopy	10'	2-6", 2-12"
2924 BZ	1-100w Med.	2924 BZ-LED	15w LED	1100	2700K	92	1-75w	8¼"	4¼"	4½" W, 8¼" H Back Plate		
2925 BZ	1-100w Med.	2925 BZ-LED	15w LED	1100	2700K	92	1-75w	10½"	5¼"	5¾" W, 10½" H Back Plate		

*Maximum achievable height with stems included. Additional stems available, 6032 BZ. For full product details and LED specifications, refer to hinkleylighting.com.

MANHATTAN™

FINISH OIL RUBBED BRONZE
GLASS CLEAR BEVELED

Manhattan is a classic update to the traditional train station lantern. The hand-painted Oil Rubbed Bronze finish complements the clean lines of its durable die cast construction.

ADDITIONAL FINISHES

Oil Rubbed Bronze with Etched Seedy glass (OZ)



2325 OZ
2325 OZ-LED
11¼" W, 18½" H





2322 OZ
2322 OZ-LED
11¼" W, 19¼" H
T24



2324 OZ
2324 OZ-LED (shown)
9¼" W, 15" H
T24



2320 OZ
2320 OZ-LED
7¼" W, 11¾" H
T24



PIER MOUNT
2327 OZ
11¼" W, 18¼" H



2321 OZ
11¼" W, 21½" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2320 OZ	1-100w Med.	2320 OZ-LED	10w LED	550	2700K	96	1-60w	8"	2½"	4½" W, 6¾" H Back Plate	
2321 OZ	1-100w Med.									3" Dia. Post Fitter	
2322 OZ	1-100w Med.	2322 OZ-LED	15w LED	800	2700K	96	1-100w			5½" Square Canopy	6', 5'
2324 OZ	1-100w Med.	2324 OZ-LED	15w LED	800	2700K	96	1-100w	10¼"	3¼"	4½" W, 6¾" H Back Plate	
2325 OZ	1-100w Med.	2325 OZ-LED	15w LED	800	2700K	96	1-100w	12½"	3¾"	7¼" W, 12" H Back Plate	
2327 OZ	1-100w Med.									9½" Square Base	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

MANHATTAN™

FINISH OIL RUBBED BRONZE
GLASS ETCHED SEEDY

Manhattan is a classic update to the traditional train station lantern. The hand-painted Oil Rubbed Bronze finish complements the clean lines of its durable die cast construction.

ADDITIONAL FINISHES

Oil Rubbed Bronze with Clear Beveled glass (OZ)



2235 OZ
2235 OZ-LED
11¼" W, 18½" H





2232 OZ
2232 OZ-LED
11¼" W, 19¼" H
T24



2234 OZ
2234 OZ-LED
9¼" W, 15" H
T24



2230 OZ
2230 OZ-LED
7¼" W, 11¾" H
T24



PIER MOUNT
2237 OZ
2237 OZ-LED
11¼" W, 18¼" H
T24



2231 OZ
2231 OZ-LED
11¼" W, 21½" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2230 OZ	1-100w Med.	2230 OZ-LED	15w LED	1100	2700K	92	1-75w	8"	2½"	4½" W, 6¾" H Back Plate	
2231 OZ	1-100w Med.	2231 OZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
2232 OZ	1-100w Med.	2232 OZ-LED	15w LED	1100	2700K	92	1-75w			5½" Square Canopy	6', 5'
2234 OZ	1-100w Med.	2234 OZ-LED	15w LED	1100	2700K	92	1-75w	10¼"	¾"	4½" W, 6¾" H Back Plate	
2235 OZ	1-100w Med.	2235 OZ-LED	15w LED	1100	2700K	92	1-75w	12½"	¾"	7¼" W, 12" H Back Plate	
2237 OZ	1-100w Med.	2237 OZ-LED	15w LED	1100	2700K	92	1-75w			9½" Square Base	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

HARBOR™

FINISH TITANIUM
GLASS ETCHED SEEDY BOUND

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the etched seedy glass.

ADDITIONAL FINISHES

Anchor Bronze (AR), Satin Black (SK)



2579 TT
2579 TT-LED
13" W, 20½" H





2572 TT
2572 TT-LED
11" W, 19" H
T24



2575 TT
2575 TT-LED
11" W, 16¼" H
T24



2573 TT
2573 TT-LED
12¼" W, 7" H
T24



2570 TT
2570 TT-LED
7" W, 10½" H
T24



2574 TT
2574 TT-LED
9" W, 13½" H
T24



PIER MOUNT
2576 TT
2576 TT-LED
11" W, 17" H
T24



2571 TT
2571 TT-LED
11" W, 19½" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2570 TT	1-60w Med.	2570 TT-LED	15w LED	1100	2700K	92	1-75w	7¾"	4¾"	4½" W, 7¼" H Back Plate	
2571 TT	1-100w Med.	2571 TT-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
2572 TT	1-100w Med.	2572 TT-LED	15w LED	1100	2700K	92	1-75w			5" Dia. Canopy	6', 5'
2573 TT	2-60w Med.	2573 TT-LED	32w LED	2300	2700K	96	2-100w				
2574 TT	1-75w Med.	2574 TT-LED	15w LED	1100	2700K	92	1-75w	10"	6¼"	4½" W, 9" H Back Plate	
2575 TT	1-100w Med.	2575 TT-LED	15w LED	1100	2700K	92	1-75w	11¾"	8"	4½" W, 12" H Back Plate	
2576 TT	1-100w Med.	2576 TT-LED	15w LED	1100	2700K	92	1-75w			8" Square Base	
2579 TT	1-100w Med.	2579 TT-LED	15w LED	1100	2700K	92	1-75w	13¼"	13¾"	4½" W, 14¼" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

HARBOR™

FINISH SATIN BLACK
GLASS ETCHED SEEDY BOUND

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the etched seedy glass.

ADDITIONAL FINISHES

Anchor Bronze (AR), Titanium (TT)



2579 SK
2579 SK-LED
13" W, 20½" H





2572 SK
2572 SK-LED
11" W, 19" H
T24



2575 SK
2575 SK-LED
11" W, 16¼" H
T24



2573 SK
2573 SK-LED
12¼" W, 7" H
T24



2570 SK
2570 SK-LED
7" W, 10½" H
T24



2574 SK
2574 SK-LED
9" W, 13½" H
T24



PIER MOUNT
2576 SK
2576 SK-LED
11" W, 17" H
T24



2571 SK
2571 SK-LED
11" W, 19½" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2570 SK	1-60w Med.	2570 SK-LED	15w LED	1100	2700K	92	1-75w	7¾"	4¾"	4½" W, 7¼" H Back Plate	
2571 SK	1-100w Med.	2571 SK-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
2572 SK	1-100w Med.	2572 SK-LED	15w LED	1100	2700K	92	1-75w			5" Dia. Canopy	6', 5'
2573 SK	2-60w Med.	2573 SK-LED	32w LED	2300	2700K	96	2-100w				
2574 SK	1-75w Med.	2574 SK-LED	15w LED	1100	2700K	92	1-75w	10"	6¼"	4½" W, 9" H Back Plate	
2575 SK	1-100w Med.	2575 SK-LED	15w LED	1100	2700K	92	1-75w	11¾"	8"	4½" W, 12" H Back Plate	
2576 SK	1-100w Med.	2576 SK-LED	15w LED	1100	2700K	92	1-75w			8" Square Base	
2579 SK	1-100w Med.	2579 SK-LED	15w LED	1100	2700K	92	1-75w	13¼"	13¾"	4½" W, 14¼" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

HARBOR™

FINISH ANCHOR BRONZE
GLASS ETCHED AMBER
SEEDY BOUND

Harbor has an updated nautical feel, with a style inspired by the clean, strong lines of a welcoming lighthouse. The cast aluminum and brass construction is accented by bold stripes against the etched amber seedy glass.

ADDITIONAL FINISHES

Satin Black (SK), Titanium (TT)



2579 AR
2579 AR-LED
13" W, 20½" H





2572 AR
2572 AR-LED
11" W, 19" H
T24



2575 AR
2575 AR-LED
11" W, 16¼" H
T24



2573 AR
2573 AR-LED
12¼" W, 7" H
T24



2570 AR
2570 AR-LED
7" W, 10½" H
T24



2574 AR
2574 AR-LED
9" W, 13½" H
T24



PIER MOUNT
2576 AR
2576 AR-LED
11" W, 17" H
T24



2571 AR
2571 AR-LED
11" W, 19½" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2570 AR	1-60w Med.	2570 AR-LED	15w LED	1100	2700K	92	1-75w	7¾"	4¾"	4½" W, 7¼" H Back Plate	
2571 AR	1-100w Med.	2571 AR-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
2572 AR	1-100w Med.	2572 AR-LED	15w LED	1100	2700K	92	1-75w			5" Dia. Canopy	6', 5'
2573 AR	2-60w Med.	2573 AR-LED	32w LED	2300	2700K	96	2-100w				
2574 AR	1-75w Med.	2574 AR-LED	15w LED	1100	2700K	92	1-75w	10"	6¼"	4½" W, 9" H Back Plate	
2575 AR	1-100w Med.	2575 AR-LED	15w LED	1100	2700K	92	1-75w	11¾"	8"	4½" W, 12" H Back Plate	
2576 AR	1-100w Med.	2576 AR-LED	15w LED	1100	2700K	92	1-75w			8" Square Base	
2579 AR	1-100w Med.	2579 AR-LED	15w LED	1100	2700K	92	1-75w	13¼"	13¾"	4½" W, 14¼" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

CHERRY CREEK™

FINISH OIL RUBBED BRONZE
GLASS WHITE LINEN

Cherry Creek's modern take on the popular Arts & Crafts style has a timeless appeal. The cast aluminum construction is enhanced by the warmth of the finish and the vintage-looking white linen glass.



ADDITIONAL FINISHES
Vintage Black (VK)





1275 OZ-WH
1275 OZ-WH-LED
12" W, 20½" H







1270 OZ-WH
1270 OZ-WH-LED
6½" W, 11" H
 





1273 OZ-WH
1273 OZ-WH-LED
12" W, 7¼" H
 





1272 OZ-WH
1272 OZ-WH-LED
12" W, 20¾" H
 



1274 OZ-WH
1274 OZ-WH-LED
8½" W, 15¼" H
 



1271 OZ-WH
1271 OZ-WH-LED
12" W, 22¼" H
 

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	TOP TO EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1270 OZ-WH	1-60w Med.	1270 OZ-WH-LED	15w LED	1100	2700K	92	1-75w	7¼"	4¼"	4½" W, 7" H Back Plate	
1271 OZ-WH	1-100w Med.	1271 OZ-WH-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1272 OZ-WH	1-100w Med.	1272 OZ-WH-LED	15w LED	1100	2700K	92	1-75w			5½" Dia. Canopy	6', 5'
1273 OZ-WH	2-60w Med.	1273 OZ-WH-LED	32w LED	2300	2700K	96	2-100w				
1274 OZ-WH	1-75w Med.	1274 OZ-WH-LED	15w LED	1100	2700K	92	1-75w	9¼"	5"	4½" W, 10" H Back Plate	
1275 OZ-WH	1-100w Med.	1275 OZ-WH-LED	15w LED	1100	2700K	92	1-75w	12¾"	6½"	5" W, 13" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

CHERRY CREEK™

FINISH VINTAGE BLACK
GLASS WHITE LINEN

Cherry Creek's modern take on the popular Arts & Crafts style has a timeless appeal. The cast aluminum construction is enhanced by the warmth of the finish and the vintage-looking white linen glass.

ADDITIONAL FINISHES

Oil Rubbed Bronze with White glass (OZ)



1275 VK
1275 VK-LED
12" W, 20½" H





1270 VK
1270 VK-LED
6½" W, 11" H
T24



1273 VK
1273 VK-LED
12" W, 7¼" H
T24



1272 VK
1272 VK-LED
12" W, 20¾" H
T24



1274 VK
1274 VK-LED
8½" W, 15¼" H
T24



1271 VK
1271 VK-LED
12" W, 22¼" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1270 VK	1-60w Med.	1270 VK-LED	15w LED	1100	2700K	92	1-75w	7¼"	4¼"	4½" W, 7" H Back Plate	
1271 VK	1-100w Med.	1271 VK-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1272 VK	1-100w Med.	1272 VK-LED	15w LED	1100	2700K	92	1-75w			5½" Dia. Canopy	6', 5'
1273 VK	2-60w Med.	1273 VK-LED	32w LED	2300	2700K	96	2-100w				
1274 VK	1-75w Med.	1274 VK-LED	15w LED	1100	2700K	92	1-75w	9¼"	5"	4½" W, 10" H Back Plate	
1275 VK	1-100w Med.	1275 VK-LED	15w LED	1100	2700K	92	1-75w	12¾"	6½"	5" W, 13" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

LEDGEWOOD™

FINISH MUSEUM BRONZE
GLASS CHAMPAGNE INSIDE ETCHED

Ledgewood's bold cast aluminum construction features a unique oval shaped, overscaled design with elegant, clean line details.



1129 MR
13" W, 19½" H



1122 MR
13" W, 19½" H



1124 MR
8" W, 12" H



1125 MR
10" W, 15½" H



1126 MR
6½" W, 7¼" H



1120 MR
7½" W, 10½" H



1121 MR
13" W, 20¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1120 MR	1-60w Med.	6½"	6"	4½" W, 7" H Back Plate	6', 5'
1121 MR	1-100w Med.			3" Dia. Post Fitter	
1122 MR	1-100w Med.	5" Dia. Canopy			
1124 MR	1-75w Med.	7¼"	6¾"	4½" W, 10" H Back Plate	
1125 MR	1-100w Med.	9¼"	8¾"	4½" W, 10" H Back Plate	
1126 MR	1-60w Med.	6"	3¾"	4½" W, 5½" H Back Plate	
1129 MR	1-100w Med.	11¼"	11"	5" W, 13" H Back Plate	

For posts and pier mounts, see pages 664-665.

CASTELLE™

FINISH BLACK
GLASS RIBBED ETCHED
CYLINDER AND ETCHED
CORNER PANELS

Castelle's transitional style in cast aluminum features clean lines and a ribbed etched glass cylinder accented by etched corner panels, adding to its sophisticated look.

ADDITIONAL FINISHES

Bronze (BZ)



1395 BK
1395 BK-LED
7" W, 18" H



1396 BK
1396 BK-LED
6" W, 11½" H



1391 BK
1391 BK-LED
7" W, 16½" H



PIER MOUNT
1397 BK
1397 BK-LED
8½" W, 12¾" H



1390 BK
1390 BK-LED
6" W, 15" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
1390 BK	1-100w Med.	1390 BK-LED	15w LED	1100	2700K	92	1-75w	7"	6¼"	4¼" W, 12¼" H Back Plate
1391 BK	1-100w Med.	1391 BK-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter
1395 BK	1-100w Med.	1395 BK-LED	15w LED	1100	2700K	92	1-75w	8¼"	7"	4¾" W, 15" H Back Plate
1396 BK	1-75w Med.	1396 BK-LED	15w LED	1100	2700K	92	1-75w	7"	4¾"	4¼" W, 8¾" H Back Plate
1397 BK	1-100w Med.	1397 BK-LED	15w LED	1100	2700K	92	1-75w			8½" Square Base

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

Castelle's transitional style in cast aluminum features clean lines and a ribbed etched amber glass cylinder accented by etched amber corner panels, adding to its sophisticated look.

FINISH BRONZE
GLASS RIBBED ETCHED
AMBER CYLINDER AND
ETCHED AMBER
CORNER PANELS

CASTELLE™

ADDITIONAL FINISHES
Black (BK)



1396 BZ
1396 BZ-LED
6" W, 11½" H



1395 BZ
1395 BZ-LED
7" W, 18" H



1390 BZ
1390 BZ-LED
6" W, 15" H



PIER MOUNT
1397 BZ
1397 BZ-LED
8½" W, 12¾" H



1391 BZ
1391 BZ-LED
7" W, 16½" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
1390 BZ	1-100w Med.	1390 BZ-LED	15w LED	1100	2700K	92	1-75w	7"	6¼"	4¼" W, 12¼" H Back Plate
1391 BZ	1-100w Med.	1391 BZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter
1395 BZ	1-100w Med.	1395 BZ-LED	15w LED	1100	2700K	92	1-75w	8¼"	7"	4¾" W, 15" H Back Plate
1396 BZ	1-75w Med.	1396 BZ-LED	15w LED	1100	2700K	92	1-75w	7"	4¾"	4¼" W, 8¾" H Back Plate
1397 BZ	1-100w Med.	1397 BZ-LED	15w LED	1100	2700K	92	1-75w			8½" Square Base

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

TUCKER™

FINISH MUSEUM BLACK
GLASS CLEAR SEEDY

Tucker is a study in symmetry with clean geometric lines and proportions reinforced throughout its cast aluminum construction. The sturdy Museum Black finish and clear seedy glass inspire a rustic lodge aesthetic.

ADDITIONAL FINISHES

Oil Rubbed Bronze (OZ)



1965 MB
1965 MB-LED
11" W, 18" H



1960 MB
1960 MB-LED
7" W, 11½" H



1961 MB
1961 MB-LED
11" W, 20½" H



1964 MB
1964 MB-LED
9" W, 14¾" H



1962 MB
1962 MB-LED
11" W, 17½" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1960 MB	1-100w Med.	1960 MB-LED	15w LED	1100	2700K	92	1-75w	8"	2¼"	4½" W, 5½" H Back Plate	
1961 MB	1-100w Med.	1961 MB-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1962 MB	1-100w Med.	1962 MB-LED	15w LED	1100	2700K	92	1-75w			5" Square Canopy	6', 5'
1964 MB	1-75w Med.	1964 MB-LED	15w LED	1100	2700K	92	1-75w	10¼"	3"	4½" W, 6¾" H Back Plate	
1965 MB	1-100w Med.	1965 MB-LED	15w LED	1100	2700K	92	1-75w	12¼"	3¾"	5½" W, 8¼" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

Tucker is a study in symmetry with clean geometric lines and proportions reinforced throughout its cast aluminum construction. The sturdy Oil Rubbed Bronze finish and clear seedy glass inspire a rustic lodge aesthetic.

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

TUCKER™

ADDITIONAL FINISHES
Museum Black (MB)



1960 OZ
1960 OZ-LED
7" W, 11½" H
T24

1965 OZ
1965 OZ-LED
11" W, 18" H
T24

1962 OZ
1962 OZ-LED
11" W, 17½" H
T24

1964 OZ
1964 OZ-LED
9" W, 14¾" H
T24

1961 OZ
1961 OZ-LED
11" W, 20½" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1960 OZ	1-100w Med.	1960 OZ-LED	15w LED	1100	2700K	92	1-75w	8"	2¼"	4½" W, 5½" H Back Plate	
1961 OZ	1-100w Med.	1961 OZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1962 OZ	1-100w Med.	1962 OZ-LED	15w LED	1100	2700K	92	1-75w			5" Square Canopy	6', 5'
1964 OZ	1-75w Med.	1964 OZ-LED	15w LED	1100	2700K	92	1-75w	10¼"	3"	4½" W, 6¾" H Back Plate	
1965 OZ	1-100w Med.	1965 OZ-LED	15w LED	1100	2700K	92	1-75w	12¼"	3¾"	5½" W, 8¼" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

RANDOLPH™

FINISH BLACK

GLASS CLEAR SEEDY GLASS PANELS,
ETCHED SEEDY GLASS PANELS

Randolph's traditional design features a bold oval pattern in die cast aluminum construction that complements a variety of exteriors.



1495 BK
11" W, 19½" H
(shown with etched
seedy glass)



1492 BK
8" W, 14" H
(shown with clear
seedy glass)



1494 BK
8" W, 14½" H
(shown with clear
seedy glass)



1490 BK
6" W, 10¾" H
(shown with etched
seedy glass)



1491 BK
8" W, 16¼" H
(shown with etched
seedy glass)



1499 BK
11" W, 20¾" H
(shown with clear
seedy glass)

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1490 BK	1-75w Med.	7"	2¼"	4½" W, 6" H Back Plate	
1491 BK	1-100w Med.			3" Dia. Post Fitter	
1492 BK	1-100w Med.			5" Square Canopy	6', 5'
1494 BK	1-100w Med.	9"	3¼"	5¼" W, 8" H Back Plate	
1495 BK	1-100w Med.	12"	3¼"	7" W, 11" H Back Plate	
1499 BK	1-100w Med.			3" Dia. Post Fitter	

For posts and pier mounts, see pages 664-665.

TAHOE™

FINISH REGENCY BRONZE
GLASS CLEAR SEEDY WATER GLASS WITH
COPPER FOIL ART GLASS ACCENTS

Tahoe makes a classic Arts & Crafts design statement in cast aluminum construction with panels of clear seedy water glass and copper foil art glass accents.



2244 RB
12" W, 22½" H



2242 RB
12" W, 22½" H



2240 RB
8½" W, 17" H



2243 RB
9½" W, 6" H



2246 RB
6½" W, 12" H



2241 RB
12" W, 22¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2240 RB	3-40w Cand.	11"	9¾"	4½" W, 14¼" H Back Plate	
2241 RB	4-40w Cand.			3" Dia. Post Fitter	
2242 RB	4-40w Cand.			5½" Dia. Canopy	6', 5'
2243 RB	2-60w Med.				
2244 RB	4-40w Cand.	14¾"	13¼"	4½" W, 18¼" H Back Plate	
2246 RB	1-60w Med.	9"	7½"	4½" W, 9¼" H Back Plate	

For posts and pier mounts, see pages 664-665.

HADLEY™

FINISH BUCKEYE BRONZE
GLASS CLEAR SEEDY

Hadley is a retro-styled collection that embodies transitional chic and will flatter any facade. Constructed of solid, die-casted aluminum, the clean lines and boldly proportioned glass create a design that would be equally at home on an Arts and Crafts cottage or a beachfront abode.



1625 KZ
11¼" W, 15" H



1622 KZ
9" DIA., 13¾" H



1624 KZ
9" W, 12½" H



1620 KZ
7¾" W, 9¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1620 KZ	1-100w Med.	8½"	3¾"	4¾" W, 7¼" H Back Plate	
1622 KZ	1-100w Med.			5¾" Dia. Canopy	6', 5'
1624 KZ	1-100w Med.	10"	3¾"	4¾" W, 7¼" H Back Plate	
1625 KZ	3-60w Cand.	12"	3¾"	4¾" W, 7¼" H Back Plate	

Ideal for vintage filament bulbs (not included).

Hudson is a transitional collection with a subtle Arts & Crafts aesthetic. The clean, minimal solid aluminum metal work has a modern feel while the shallow roof lines and cast vertical posts add a refined craftsman touch.

FINISH OIL RUBBED BRONZE
GLASS ETCHED OPAL

HUDSON™



1912 OZ
11" DIA., 15½" H



1915 OZ
11" W, 13½" H



1910 OZ
7" W, 9¾" H



1914 OZ
9" W, 12" H



1911 OZ
11" DIA., 16¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1910 OZ	1-100w Med.	8"	4¼"	4½" W, 8¼" H Back Plate	
1911 OZ	1-100w Med.			3" Dia. Post Fitter	
1912 OZ	1-100w Med.			5" Dia. Canopy	6', 5'
1914 OZ	1-100w Med.	10"	4¼"	4½" W, 8¼" H Back Plate	
1915 OZ	1-100w Med.	12"	4¼"	4½" W, 8¼" H Back Plate	

For posts and pier mounts, see pages 664-665.

QUINCY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY AND AMBER

Quincy's traditional bell-shaped design in die cast aluminum construction evokes early Americana. The seedy outer glass and interior amber cylinder, acting as a "faux" candle, adds to its nostalgic feel.

ADDITIONAL FINISHES

Aged Zinc (DZ)



2615 OZ
2615 OZ-LED
9¼" W, 16¾" H



2614 OZ
2614 OZ-LED
6¾" W, 13½" H



2612 OZ
2612 OZ-LED
9¼" W, 15½" H



2611 OZ
2611 OZ-LED
9¼" W, 18¾" H



2618 OZ
2618 OZ-LED
11" W, 20" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2611 OZ	1-100w Med.	2611 OZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
2612 OZ	1-100w Med.	2612 OZ-LED	15w LED	1100	2700K	92	1-75w			5" Dia. Canopy	6', 5'
2614 OZ	1-100w Med.	2614 OZ-LED	15w LED	1100	2700K	92	1-75w	8"	8"	5" W, 12" H Back Plate	
2615 OZ	1-100w Med.	2615 OZ-LED	15w LED	1100	2700K	92	1-75w	10¾"	9¼"	4¾" W, 15¼" H Back Plate	
2618 OZ	1-100w Med.	2618 OZ-LED	15w LED	1100	2700K	92	1-75w	12½"	10¾"	4¾" W, 18½" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

Quincy's traditional bell-shaped design in die cast aluminum construction evokes early Americana. The seedy outer glass and interior etched opal cylinder, acting as a "faux" candle, adds to its nostalgic feel.

FINISH AGED ZINC
GLASS CLEAR SEEDY AND
ETCHED OPAL

QUINCY™

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



2612 DZ
2612 DZ-LED
9¼" W, 15½" H



2614 DZ
2614 DZ-LED
6¾" W, 13½" H



2615 DZ
2615 DZ-LED
9¼" W, 16¾" H



2618 DZ
2618 DZ-LED
11" W, 20" H



2611 DZ
2611 DZ-LED
9¼" W, 18¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2611 DZ	1-100w Med.	2611 DZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
2612 DZ	1-100w Med.	2612 DZ-LED	15w LED	1100	2700K	92	1-75w			5" Dia. Canopy	6', 5'
2614 DZ	1-100w Med.	2614 DZ-LED	15w LED	1100	2700K	92	1-75w	8"	8"	5" W, 12" H Back Plate	
2615 DZ	1-100w Med.	2615 DZ-LED	15w LED	1100	2700K	92	1-75w	10¾"	9¼"	4¾" W, 15¼" H Back Plate	
2618 DZ	1-100w Med.	2618 DZ-LED	15w LED	1100	2700K	92	1-75w	12½"	10¾"	4¾" W, 18½" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

RILEY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY AND
 ETCHED OPAL

Riley's shallow roof, arm and metal scroll bring a refined Arts & Crafts element to its aluminum construction. The seedy outer glass and inner etched opal glass offer a unique 'layered light' effect.



2012 OZ
 2012 OZ-LED
 11" DIA., 14" H
 



2015 OZ
 2015 OZ-LED
 11" W, 18¾" H
 



2010 OZ
 2010 OZ-LED
 9" W, 17½" H
 



2011 OZ
 2011 OZ-LED
 11" DIA., 18½" H
 


ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2010 OZ	1-100w Med.	2010 OZ-LED	15w LED	1100	2700K	92	1-75w	10¾"	7¾"	6½" Dia. Back Plate	
2011 OZ	1-100w Med.	2011 OZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
2012 OZ	1-100w Med.	2012 OZ-LED	15w LED	1100	2700K	92	1-75w			5" Dia. Canopy	6', 5'
2015 OZ	1-100w Med.	2015 OZ-LED	15w LED	1100	2700K	92	1-75w	12¾"	8½"	6½" Dia. Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

Mondrian's unique patterned glass adds a geometric panache to the durable brass and aluminum construction. These chic pocket style wall mounted lanterns are ADA compliant.

FINISH BUCKEYE BRONZE
GLASS ART GLASS PANELS


MONDRIAN™



2154 KZ
9" W, 14¼" H



2155 KZ
7" W, 24" H



2150 KZ
7" W, 11" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2150 KZ	1-60w Cand.	4"	5½"	7" W, 10¼" H
2154 KZ	2-60w Cand.	4"	7¼"	9" W, 13½" H
2155 KZ	3-60w Cand.	4"	12"	7" W, 23" H

SULLIVAN™


FINISH BLACK
GLASS ETCHED OPAL

Sullivan's clean transitional style features a minimalist cast aluminum body that frames the contemporary, candle-like etched opal glass. A large cast ring finial is mounted on top for a traditional finishing touch to this sleek lantern design.

ADDITIONAL FINISHES

Hematite (HE), Oil Rubbed Bronze (OZ)

INSTAFAVE



@emilyaclarck

THE SULLIVAN COLLECTION



1745 BK
1745 BK-LED
11¾" W, 23" H



1742 BK
1742 BK-LED
11¾" W, 23" H



1741 BK
1741 BK-LED
11¾" W, 26" H



1744 BK
1744 BK-LED
9" W, 18¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1741 BK	1-100w Med.	1741 BK-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1742 BK	1-100w Med.	1742 BK-LED	15w LED	1100	2700K	92	1-75w			4½" Square Canopy	6', 5'
1744 BK	1-100w Med.	1744 BK-LED	15w LED	1100	2700K	92	1-75w	10"	11¾"	5" W, 11¾" H Back Plate	
1745 BK	1-100w Med.	1745 BK-LED	15w LED	1100	2700K	92	1-75w	12¾"	15¼"	5" W, 15¼" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

Sullivan's clean transitional style features a minimalist cast aluminum body that frames the contemporary, candle-like etched opal glass. A large cast ring finial is mounted on top for a traditional finishing touch to this sleek lantern design.

FINISH HEMATITE
GLASS ETCHED OPAL

SULLIVAN™

ADDITIONAL FINISHES
Black (BK), Oil Rubbed Bronze (OZ)



1742 HE
1742 HE-LED
11¾" W, 23" H
T24



1745 HE
1745 HE-LED
11¾" W, 23" H
T24



1744 HE
1744 HE-LED
9" W, 18¼" H
T24



1741 HE
1741 HE-LED
11¾" W, 26" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1741 HE	1-100w Med.	1741 HE-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1742 HE	1-100w Med.	1742 HE-LED	15w LED	1100	2700K	92	1-75w			4½" Square Canopy	6', 5'
1744 HE	1-100w Med.	1744 HE-LED	15w LED	1100	2700K	92	1-75w	10"	11¾"	5" W, 11¾" H Back Plate	
1745 HE	1-100w Med.	1745 HE-LED	15w LED	1100	2700K	92	1-75w	12¾"	15¼"	5" W, 15¼" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

SULLIVAN™

FINISH OIL RUBBED BRONZE
GLASS ETCHED OPAL

Sullivan's clean transitional style features a minimalist cast aluminum body that frames the contemporary, candle-like etched opal glass. A large cast ring finial is mounted on top for a traditional finishing touch to this sleek lantern design.

ADDITIONAL FINISHES
Black (BK), Hematite (HE)



1741 OZ
1741 OZ-LED
11¾" W, 26" H
T24

1745 OZ
1745 OZ-LED
11¾" W, 23" H
T24

1744 OZ
1744 OZ-LED
9" W, 18¼" H
T24

1742 OZ
1742 OZ-LED
11¾" W, 23" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1741 OZ	1-100w Med.	1741 OZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1742 OZ	1-100w Med.	1742 OZ-LED	15w LED	1100	2700K	92	1-75w			4½" Square Canopy	6', 5'
1744 OZ	1-100w Med.	1744 OZ-LED	15w LED	1100	2700K	92	1-75w	10"	11¾"	5" W, 11¾" H Back Plate	
1745 OZ	1-100w Med.	1745 OZ-LED	15w LED	1100	2700K	92	1-75w	12¾"	15¼"	5" W, 15¼" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

Theo's robust frame features precision die-cast components and a sturdy mesh cage that creates a welcoming glow from its high-performance LED technology. The transitional style adds a layer of industrial chic that is at home on a variety of exteriors.

FINISH OIL RUBBED BRONZE
SHADE WIRE MESH

THEO™

exclusively available in
HIGH-PERFORMANCE LED 



2742 OZ
8" W, 11¼" H
 



2740 OZ
6" W, 9" H
 



2745 OZ
8" W, 14" H
 



2744 OZ
8" W, 11¾" H
 

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2740 OZ	13w LED	700	2700K	80	1-60w	7½"	2¼"	4½" W, 5½" H Back Plate	
2742 OZ	13w LED	700	2700K	80	1-60w			5" Square Canopy	6', 5'
2744 OZ	13w LED	700	2700K	80	1-60w	9¾"	2½"	4½" W, 6¾" H Back Plate	
2745 OZ	13w LED	700	2700K	80	1-60w	9¾"	2½"	4½" W, 6¾" H Back Plate	

For full product details and LED specifications, refer to hinkleylighting.com.

BURKE™

FINISH OIL RUBBED BRONZE
GLASS ETCHED WHITE

Burke's design has its roots in American Arts and Crafts architecture. A focus on solid construction, craftsmanship and clean lines make this impeccable design a fitting addition to almost any façade or outdoor living area.

ADDITIONAL FINISHES

Oil Rubbed Bronze with Clear Seedy Glass (OZ-CL)



2790 OZ
7¼" W, 10¾" H



2795 OZ
10¼" W, 18½" H



2791 OZ
9" W, 16" H



2794 OZ
9" W, 14" H



2792 OZ
9" W, 13" H
54½" MAX. H*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
2790 OZ	1-100w Med.	7½"	2¾"	4½" W, 5½" H Back Plate		
2791 OZ	1-100w Med.			3" Dia. Post Fitter		
2792 OZ	1-100w Med.			5" Dia. Canopy	10'	2-6", 2-12"
2794 OZ	1-100w Med.	9¾"	3½"	4½" W, 6¾" H Back Plate		
2795 OZ	1-100w Med.	9¾"	3½"	4½" W, 6¾" H Back Plate		

*Maximum achievable height with stems included. Additional stems available, 6032 OZOD. For posts and pier mounts, see pages 664-665.

Burke's design has its roots in American Arts and Crafts architecture. A focus on solid construction, craftsmanship and clean lines make this impeccable design a fitting addition to almost any façade or outdoor living area.

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

BURKE™

ADDITIONAL FINISHES
Oil Rubbed Bronze with Etched White Glass (OZ)



2792 OZ-CL
9" W, 13" H
54½" MAX. H*



2795 OZ-CL
10¼" W, 18½" H



2790 OZ-CL
7¼" W, 10¾" H



2794 OZ-CL
9" W, 14" H



2791 OZ-CL
9" W, 16" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
2790 OZ-CL	1-100w Med.	7½"	2¾"	4½" W, 5½" H Back Plate		
2791 OZ-CL	1-100w Med.			3" Dia. Post Fitter		
2792 OZ-CL	1-100w Med.			5" Dia. Canopy	10'	2-6", 2-12"
2794 OZ-CL	1-100w Med.	9¾"	3½"	4½" W, 6¾" H Back Plate		
2795 OZ-CL	1-100w Med.	9¾"	3½"	4½" W, 6¾" H Back Plate		

*Maximum achievable height with stems included. Additional stems available, 6032 OZOD. Ideal for vintage filament bulbs (not included). For posts and pier mounts, see pages 664-665.

WALKER™

FINISH BUCKEYE BRONZE
WITH HERITAGE BRASS
GLASS BOUND CLEAR

Walker has roots in the American West with its large scale, strong angular lines and no-nonsense style. The sturdy aluminum and brass construction features a two-tone finish of bold Buckeye Bronze and Heritage Brass, adding a transitional flair to its minimalist shape. A welded outer form frames an inner clear, bound glass shade. At home on the range, in a mountain cabin or creating a mid-century statement, this flexible style complements many façades.

ADDITIONAL FINISHES

Black with Antique Nickel (BK)




2105 KZ
2105 KZ-LL
11½" W, 17½" H





2102 KZ
2102 KZ-LL
11½" W, 17¼" H
50" MAX. H**



2106 KZ
7¼" W, 9½" H



2100 KZ
8¼" W, 12¼" H



2104 KZ
2104 KZ-LL
9½" W, 15" H



2101 KZ
2101 KZ-LL
11¼" W, 20¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
2100 KZ	1-100w Med.			9¼"	3½"	4½" W, 7" H Back Plate		
2101 KZ	3-60w Cand.	2101 KZ-LL	3-5w Cand. LED*			3" Dia. Post Fitter		
2102 KZ	3-60w Cand.	2102 KZ-LL	3-5w Cand. LED*			5" Dia. Canopy	10'	1-6", 2-12"
2104 KZ	2-60w Cand.	2104 KZ-LL	2-5w Cand. LED*	10¼"	4"	4½" W, 8" H Back Plate		
2105 KZ	3-60w Cand.	2105 KZ-LL	3-5w Cand. LED*	12"	4½"	5" W, 9" H Back Plate		
2106 KZ	1-100w Med.			8¼"	2½"	4½" W, 5¼" H Back Plate		

*LED filament bulb included, see page 7. **Maximum achievable height with stems included. Additional stems available, 6212 HB4. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

WALKER™

FINISH BLACK WITH
ANTIQUÉ NICKEL
GLASS BOUND CLEAR

Walker has roots in the American West with its large scale, strong angular lines and no-nonsense style. The sturdy aluminum and brass construction features a two-tone finish of bold Black and Antique Nickel, adding a transitional flair to its minimalist shape. A welded outer form frames an inner clear, bound glass shade. At home on the range, in a mountain cabin or creating a mid-century statement, this flexible style complements many façades.

ADDITIONAL FINISHES

Buckeye Bronze with Heritage Brass (KZ)



2105 BK
2105 BK-LL
11½" W, 17½" H





2102 BK
2102 BK-LL
11½" W, 17¼" H
50" MAX. H**



2104 BK
2104 BK-LL
9½" W, 15" H



2106 BK
7½" W, 9½" H



2100 BK
8½" W, 12¼" H



2101 BK
2101 BK-LL
11½" W, 20¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE	STEMS INCLUDED
2100 BK	1-100w Med.			9¼"	3½"	4½" W, 7" H Back Plate		
2101 BK	3-60w Cand.	2101 BK-LL	3-5w Cand. LED*			3" Dia. Post Fitter		
2102 BK	3-60w Cand.	2102 BK-LL	3-5w Cand. LED*			5" Dia. Canopy	10'	1-6", 2-12"
2104 BK	2-60w Cand.	2104 BK-LL	2-5w Cand. LED*	10¼"	4"	4½" W, 8" H Back Plate		
2105 BK	3-60w Cand.	2105 BK-LL	3-5w Cand. LED*	12"	4½"	5" W, 9" H Back Plate		
2106 BK	1-100w Med.			8¼"	2½"	4½" W, 5¼" H Back Plate		

*LED filament bulb included, see page 7. **Maximum achievable height with stems included. Additional stems available, 6063 ANOD4. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

BURTON™

FINISH BLACK WITH
COPPER
GLASS CLEAR BEVELED

Burton's classic cast aluminum construction in a robust Black finish is complemented by elegant touches. The distressed copper accents on the back plate, roof and socket cover paired with clear beveled glass complements the traditional styling.



1970 BK
8" W, 12¾" H



1972 BK
10" W, 18¾" H



1974 BK
10" W, 15¾" H

ITEM	MAXIMUM WATTAGE	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1970 BK	1-100w Med.	5¾"		5¼"	4½" W, 8¾" H Back Plate	
1972 BK	2-60w Cand.		6¼"		5" Dia. Canopy	6', 5'
1974 BK	2-60w Cand.	7"	6¼"	5½"	4½" W, 8¾" H Back Plate	

The Thatcher outdoor lantern by Hinkley Lighting is a nod to the authentic craftsmanship of an early American style lantern. Copper construction is enhanced by authentic rivet and latch details and the clear glass door stands out against the beautiful patina of the Antique Copper finish.

FINISH ANTIQUE COPPER
GLASS CLEAR

THATCHER™



18200 AP
8½" W, 14" H



18204 AP
10½" W, 17¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
18200 AP	2-60w Cand.	6¼"	10"	4¾" W, 6" H
18204 AP	2-60w Cand.	7½"	12¼"	4¾" W, 7" H

SUTCLIFFE™

FINISH OIL RUBBED BRONZE
WITH COPPER
GLASS CLEAR

The Sutcliffe collection conveys chic elements of early Americana styling. The candelabra lamping, clear glass and Copper reflector infuse this sleek pocket lantern design constructed of solid aluminum with a perfect blend of old and new.

ADDITIONAL FINISHES

Aged Zinc with Antique Nickel (DZ)



2911 OZ
2911 OZ-LL
10" W, 20" H



2915 OZ
2915 OZ-LL
10" W, 22" H



2910 OZ
2910 OZ-LL
7" W, 14" H



2914 OZ
2914 OZ-LL
9" W, 17" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
2910 OZ	1-60w Cand.	2910 OZ-LL	1-5w Cand. LED*	5½"	8¼"	5" W, 9" H Back Plate
2911 OZ	3-60w Cand.	2911 OZ-LL	3-5w Cand. LED*			3" Dia. Post Fitter
2914 OZ	2-60w Cand.	2914 OZ-LL	2-5w Cand. LED*	5½"	9½"	5¼" W, 11½" H Back Plate
2915 OZ	3-60w Cand.	2915 OZ-LL	3-5w Cand. LED*	6½"	12"	7" W, 15½" H Back Plate

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. Ideal for vintage filament bulbs (not included). For posts and pier mounts, see pages 664-665.

The Sutcliffe collection conveys chic elements of early Americana styling. The candelabra lamping, clear glass and Antique Nickel reflector infuse this sleek pocket lantern design constructed of solid aluminum with a perfect blend of old and new.

FINISH AGED ZINC
WITH ANTIQUE NICKEL
GLASS CLEAR

SUTCLIFFE™

ADDITIONAL FINISHES
Oil Rubbed Bronze with Copper (OZ)



2910 DZ
2910 DZ-LL
7" W, 14" H



2915 DZ
2915 DZ-LL
10" W, 22" H



2914 DZ
2914 DZ-LL
9" W, 17" H



2911 DZ
2911 DZ-LL
10" W, 20" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
2910 DZ	1-60w Cand.	2910 DZ-LL	1-5w Cand. LED*	5½"	8¼"	5" W, 9" H Back Plate
2911 DZ	3-60w Cand.	2911 DZ-LL	3-5w Cand. LED*			3" Dia. Post Fitter
2914 DZ	2-60w Cand.	2914 DZ-LL	2-5w Cand. LED*	5½"	9½"	5¼" W, 11½" H Back Plate
2915 DZ	3-60w Cand.	2915 DZ-LL	3-5w Cand. LED*	6½"	12"	7" W, 15½" H Back Plate

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. Ideal for vintage filament bulbs (not included). For posts and pier mounts, see pages 664-665.


NEWPORT™

FINISH AGED ZINC
GLASS CLEAR SEEDY


Newport is an early American classic pocket lantern featuring an optional copper reflector. Constructed in aluminum with the same quality as the traditional wharf light that served as its inspiration, the wire cage in Aged Zinc also features authentic rivet details and clear seedy glass to shield the light source.




2620 DZ
7" W, 9¼" H




2625 DZ
9" W, 16" H




2624 DZ
9" W, 12" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2620 DZ	1-60w Cand.	4"	4¾"	4½" W, 8½" H
2624 DZ	2-60w Cand.	4"	6"	4¾" W, 10¼" H
2625 DZ	3-60w Cand.	4"	8"	4¾" W, 14½" H

Inspired by ship bulkheads, Westport is a fusion of unique maritime elements. The die-cast aluminum fixture is offered as incandescent with candelabra lamping and a clear glass Fresnel lens, or as an LED version paired with an etched glass Fresnel lens. Bold finish options of Buckeye Bronze or Aged Zinc reinforce its distinctive style.

FINISH AGED ZINC,
BUCKEYE BRONZE
GLASS CLEAR OR
ETCHED FRESNEL LENS

WESTPORT™



2722 KZ
11¼" W, 12¾" H



2722 KZ-LED
11¼" W, 12¾" H



2722 KZ-LED
(mounted flush to ceiling)



2722 DZ
11¼" W, 12¾" H



2722 DZ-LED
11¼" W, 12¾" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE
2722 DZ	2-60w Cand.	2722 DZ-LED	16w LED	800	2700K	91	1-75w	4"	7"	6½" Dia.
2722 KZ	2-60w Cand.	2722 KZ-LED	16w LED	800	2700K	91	1-75w	4"	7"	6½" Dia.

For complete product details and LED specifications, refer to hinkleylighting.com.

PERRY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Named for Commodore Oliver Hazard Perry, who led a fleet to victory in one of the most significant naval battles in the War of 1812, this nautical-inspired aluminum lantern offers distinctive longitudinal and latitudinal cage construction. Clear seedy glass and a durable Oil Rubbed Bronze finish reinforce Perry's transitional style, which effortlessly complements a variety of façades.



2380 OZ
5½" W, 19¾" H



2384 OZ
8" W, 24" H



2382 OZ
5¼" W, 16" H
48½" MAX. H*



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2380 OZ	1-50w GU-10**	6¾"	10"	5" W, 6½" H Back Plate		
2382 OZ	1-50w GU-10**			5" Dia. Canopy	10'	1-6", 2-12"
2384 OZ	1-50w GU-10**	10"	11¾"	5" W, 6½" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 6061 OZOD. **GU-10 bulb included.



LISA MCDENNON
LISA MCDENNON DESIGN
LAGUNA BEACH, CA

“Nautical designs are enduring, and embody a classic, clean and bold aesthetic. There has always been an enchantment with the sea, and so many people are drawn to the ocean’s beauty and the lifestyle that surrounds coastal living.”

ABOVE: THE HARBOR COLLECTION | 2579SK, PAGE 510

REEF™

FINISH VICTORIAN BRONZE
GLASS INSIDE ETCHED

Reef's contemporary nautical shape features a sleek capsule of inside etched glass captured by bold rings of cast aluminum.

ADDITIONAL FINISHES

Hematite (HE)



1952 VZ
1952 VZ-LED
9" DIA., 15" H



1950 VZ
1950 VZ-LED
7¾" W, 10¾" H



1956 VZ
1956 VZ-LED
5½" W, 8" H



1954 VZ
1954 VZ-LED
9" W, 12¾" H



1951 VZ
1951 VZ-LED
9" DIA., 16¼" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1950 VZ	1-75w Med.	1950 VZ-LED	15w LED	1100	2700K	92	1-75w	8¾"	4"	4½" W, 7" H Back Plate	
1951 VZ	1-100w Med.	1951 VZ-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1952 VZ	1-100w Med.	1952 VZ-LED	15w LED	1100	2700K	92	1-75w			5½" Dia. Canopy	6', 5'
1954 VZ	1-100w Med.	1954 VZ-LED	15w LED	1100	2700K	92	1-75w	10"	4¼"	4½" W, 7" H Back Plate	
1956 VZ	1-60w Med.	1956 VZ-LED	15w LED	1100	2700K	92	1-75w	6½"	2½"	4½" W, 5" H Back Plate	

For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

Reef's contemporary nautical shape features a sleek capsule of inside etched glass captured by bold rings of cast aluminum.

FINISH HEMATITE
GLASS INSIDE ETCHED

REEF™

ADDITIONAL FINISHES
Victorian Bronze (VZ)



1956 HE
1956 HE-LED
5½" W, 8" H
T24



1950 HE
1950 HE-LED
7¾" W, 10¾" H
T24



1952 HE
1952 HE-LED
9" DIA., 15" H
T24



1951 HE
1951 HE-LED
9" DIA., 16¼" H
(shown as pier mount
with 1304 HE)*
T24



1954 HE
1954 HE-LED
9" W, 12¾" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1950 HE	1-75w Med.	1950 HE-LED	15w LED	1100	2700K	92	1-75w	8¾"	4"	4½" W, 7" H Back Plate	
1951 HE	1-100w Med.	1951 HE-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1952 HE	1-100w Med.	1952 HE-LED	15w LED	1100	2700K	92	1-75w			5½" Dia. Canopy	6', 5'
1954 HE	1-100w Med.	1954 HE-LED	15w LED	1100	2700K	92	1-75w	10"	4¼"	4½" W, 7" H Back Plate	
1956 HE	1-60w Med.	1956 HE-LED	15w LED	1100	2700K	92	1-75w	6½"	2½"	4½" W, 5" H Back Plate	

For complete product details and LED specifications, refer to hinkleylighting.com. *Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

MARINA™

FINISH BRONZE
GLASS CLEAR OR
ETCHED HOLOPHANE

Set sail with Marina. Inspired by authentic ship passageway lighting, its die-casted aluminum construction uniquely emphasizes the captured etched holophane or clear holophane glass. Robust finish options include Bronze or Hematite and showcase the fresh, modern-nautical cast cage design.

ADDITIONAL FINISHES

Hematite (HE)



2410 BZ
8¼" W, 11¾" H



2414 BZ
10¼" W, 14½" H



2413 BZ
10¼" W, 5" H



2480 BZ
8¼" W, 11¾" H



2484 BZ
10¼" W, 14½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2410 BZ	1-100w Med.	8½"	2½"	5" Dia.
2413 BZ	2-60w Med.			
2414 BZ	1-100w Med.	10½"	3"	6" Dia.
2480 BZ	1-100w Med.	8½"	2½"	5" Dia.
2484 BZ	1-100w Med.	10½"	3"	6" Dia.

Set sail with Marina. Inspired by authentic ship passageway lighting, its die-casted aluminum construction uniquely emphasizes the captured etched holophane or clear holophane glass. Robust finish options include Bronze or Hematite and showcase the fresh, modern-nautical cast cage design.

FINISH HEMATITE
GLASS CLEAR OR
ETCHED HOLOPHANE

MARINA™

ADDITIONAL FINISHES
Bronze (BZ)



2413 HE
10¼" W, 5" H



2414 HE
10¼" W, 14½" H



2410 HE
8¼" W, 11¾" H



2484 HE
10¼" W, 14½" H



2480 HE
8¼" W, 11¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
2410 HE	1-100w Med.	8½"	2½"	5" Dia.
2413 HE	2-60w Med.			
2414 HE	1-100w Med.	10½"	3"	6" Dia.
2480 HE	1-100w Med.	8½"	2½"	5" Dia.
2484 HE	1-100w Med.	10½"	3"	6" Dia.

FREEPORT™

FINISH CLASSIC WHITE
GLASS CLEAR SEEDY

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

ADDITIONAL FINISHES

Black (BK), Oil Rubbed Bronze (OZ), Olde Penny (OP)



1804 CW
1804 CW-LED
8" W, 12¼" H



1805 CW
1805 CW-LED
10" W, 15¼" H



1802 CW
1802 CW-LED
10" DIA., 14" H



1801 CW
1801 CW-LED
10" DIA., 20¼" H
(shown as pier mount
with 1304 CW)*



1807 CW
8" DIA., 17¾" H



1800 CW
1800 CW-LED
6" W, 9¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1800 CW	1-75w Med.	1800 CW-LED	10w LED	550	2700	96	1-60w	7"	2½"	4½" W, 6" H Back Plate	
1801 CW	1-100w Med.	1801 CW-LED	15w LED	1100	2700	92	1-75w			3" Dia. Post Fitter	
1802 CW	1-100w Med.	1802 CW-LED	15w LED	800	2700	96	1-100w			4¼" Dia. Canopy	6', 5'
1804 CW	1-100w Med.	1804 CW-LED	15w LED	800	2700	96	1-100w	9"	3"	5" W, 8" H Back Plate	
1805 CW	1-100w Med.	1805 CW-LED	15w LED	800	2700	96	1-100w	11¼"	3¼"	5¾" W, 9½" H Back Plate	
1807 CW	1-100w Med.									3" Dia. Post Fitter	

For complete product details and LED specifications, refer to hinkleylighting.com. *Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

FREEPORT™

ADDITIONAL FINISHES
Black (BK), Classic White (CW), Olde Penny (OP)



1802 OZ
1802 OZ-LED
10" DIA., 14" H
T24



1805 OZ
1805 OZ-LED
10" W, 15¼" H
T24



1804 OZ
1804 OZ-LED
8" W, 12¼" H
T24



1800 OZ
1800 OZ-LED
6" W, 9¼" H
T24



1807 OZ
8" DIA., 17¾" H



1801 OZ
1801 OZ-LED
10" DIA., 20¼" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1800 OZ	1-75w Med.	1800 OZ-LED	10w LED	550	2700	96	1-60w	7"	2½"	4½" W, 6" H Back Plate	
1801 OZ	1-100w Med.	1801 OZ-LED	15w LED	1100	2700	92	1-75w			3" Dia. Post Fitter	
1802 OZ	1-100w Med.	1802 OZ-LED	15w LED	800	2700	96	1-100w			4¼" Dia. Canopy	6', 5'
1804 OZ	1-100w Med.	1804 OZ-LED	15w LED	800	2700	96	1-100w	9"	3"	5" W, 8" H Back Plate	
1805 OZ	1-100w Med.	1805 OZ-LED	15w LED	800	2700	96	1-100w	11¼"	3¼"	5¾" W, 9½" H Back Plate	
1807 OZ	1-100w Med.									3" Dia. Post Fitter	

For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

FREEPORT™

FINISH BLACK
GLASS CLEAR SEEDY

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

ADDITIONAL FINISHES

Classic White (CW), Oil Rubbed Bronze (OZ), Olde Penny (OP)



1804 BK
1804 BK-LED
8" W, 12¼" H



1805 BK
1805 BK-LED
10" W, 15¼" H



1802 BK
1802 BK-LED
10" DIA., 14" H



1801 BK
1801 BK-LED
10" DIA., 20¼" H



1807 BK
8" DIA., 17¾" H



1800 BK
1800 BK-LED
6" W, 9¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1800 BK	1-75w Med.	1800 BK-LED	10w LED	550	2700	96	1-60w	7"	2½"	4½" W, 6" H Back Plate	
1801 BK	1-100w Med.	1801 BK-LED	15w LED	1100	2700	92	1-75w			3" Dia. Post Fitter	
1802 BK	1-100w Med.	1802 BK-LED	15w LED	800	2700	96	1-100w			4¼" Dia. Canopy	6', 5'
1804 BK	1-100w Med.	1804 BK-LED	15w LED	800	2700	96	1-100w	9"	3"	5" W, 8" H Back Plate	
1805 BK	1-100w Med.	1805 BK-LED	15w LED	800	2700	96	1-100w	11¼"	3¼"	5¾" W, 9½" H Back Plate	
1807 BK	1-100w Med.									3" Dia. Post Fitter	

For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

Freeport features a classic New England design in cast aluminum construction for timeless, traditional style.

FINISH OLDE PENNY
GLASS ETCHED SEEDY

FREEPORT™

ADDITIONAL FINISHES
Black (BK), Classic White (CW), Oil Rubbed Bronze (OZ)



1802 OP
1802 OP-LED
10" DIA., 14" H
T24



1805 OP
1805 OP-LED
10" W, 15¼" H
T24



1804 OP
1804 OP-LED
8" W, 12¼" H
T24



1800 OP
1800 OP-LED
6" W, 9¼" H
T24



1807 OP
8" DIA., 17¾" H



1801 OP
1801 OP-LED
10" DIA., 20¼" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1800 OP	1-75w Med.	1800 OP-LED	10w LED	550	2700	96	1-60w	7"	2½"	4½" W, 6" H Back Plate	
1801 OP	1-100w Med.	1801 OP-LED	15w LED	1100	2700	92	1-75w			3" Dia. Post Fitter	
1802 OP	1-100w Med.	1802 OP-LED	15w LED	800	2700	96	1-100w			4¼" Dia. Canopy	6', 5'
1804 OP	1-100w Med.	1804 OP-LED	15w LED	800	2700	96	1-100w	9"	3"	5" W, 8" H Back Plate	
1805 OP	1-100w Med.	1805 OP-LED	15w LED	800	2700	96	1-100w	11¼"	3¼"	5¾" W, 9½" H Back Plate	
1807 OP	1-100w Med.									3" Dia. Post Fitter	

For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

NEW CASTLE™

FINISH BLACK
GLASS CLEAR SEEDY

The New Castle collection gives this traditional lantern design a modern twist with a recessed light source inside a seedy glass cylinder. The solid aluminum construction in a durable powder coat Black finish is Dark Sky compliant.



2258 BK
11" W, 24" H





2252 BK
11" DIA., 15" H



2255 BK
11" W, 19½" H



2250 BK
7" W, 9¾" H



2254 BK
9" W, 16¾" H



2251 BK
11" W, 22¼" H



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2250 BK	1-35w GU-10*	8"	5¾"	4½" W, 6¾" H Back Plate	
2251 BK	1-50w GU-10*			3" Dia. Post Fitter	
2252 BK	1-50w GU-10*			5½" Dia. Canopy	6', 5'
2254 BK	1-50w GU-10*	10"	11¼"	4½" W, 6¾" H Back Plate	
2255 BK	1-50w GU-10*	12¼"	12¼"	4½" W, 6¾" H Back Plate	
2258 BK	1-50w GU-10*	12¼"	12¼"	4½" W, 6¾" H Back Plate	

*GU-10 bulbs included. For posts and pier mounts, see pages 664-665.



Calistoga's historically-inspired design combines the vintage appeal of a classic pioneer lantern with updated lines and construction. This solid aluminum collection features a rich Spanish Bronze finish and clear seeded glass globe for authentic charm.

FINISH SPANISH BRONZE
GLASS CLEAR SEEDY

CALISTOGA™



2092 SB
9¾" W, 16¼" H

2095 SB
9¾" W, 18¾" H

2090 SB
8½" W, 16¼" H

2094 SB
9" W, 17¾" H

2091 SB
9¾" W, 26" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2090 SB	1-100w Med.	9¾"	7¼"	6" Dia. Back Plate	
2091 SB	1-100w Med.			3" Dia. Post Fitter	
2092 SB	1-100w Med.			5" Dia. Canopy	6', 5'
2094 SB	1-100w Med.	9¾"	7¼"	6" Dia. Back Plate	
2095 SB	1-100w Med.	9¾"	7¼"	6" Dia. Back Plate	

For posts and pier mounts, see pages 664-665.

CAPE COD™

FINISH AGED ZINC
GLASS CLEAR SEEDY

Cape Cod's classic onion lantern design conveys classic New England style. The solid aluminum construction and clear seedy glass add vintage appeal.

ADDITIONAL FINISHES
Sienna Bronze (SZ)



2205 DZ
13½" W, 26¾" H



2202 DZ
11" DIA., 19¼" H



2203 DZ
7" W, 9" H



2200 DZ
8½" W, 18" H



2206 DZ
7" W, 14" H



2204 DZ
10¾" W, 23¼" H



2207 DZ
11" DIA., 21¼" H
(shown as pier mount
with 1304 DZ)*



2201 DZ
13¾" DIA., 23¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2200 DZ	1-75w Med.	10¼"	11½"	5½" W, 5½" H Back Plate	
2201 DZ	4-40w Cand.			3" Dia. Post Fitter	
2202 DZ	1-100w Med.			5" Dia. Canopy	6', 5'
2203 DZ	1-60w Med.			5" Dia. Canopy	6', 5'
2204 DZ	1-100w Med.	13"	16"	4½" W, 9½" H Back Plate	
2205 DZ	1-100w Med.	15"	17¼"	4½" W, 10" H Back Plate	
2206 DZ	1-60w Med.	8"	9¼"	4¼" W, 5½" H Back Plate	
2207 DZ	3-40w Cand.			3" Dia. Post Fitter	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665. Ideal for vintage filament bulbs (not included).

CAPE COD™

FINISH SIENNA BRONZE
GLASS CLEAR SEEDY

Cape Cod's classic onion lantern design conveys classic New England style. The solid brass construction and clear seedy glass add vintage appeal.

ADDITIONAL FINISHES
Aged Zinc (DZ)



2205 SZ
13½" W, 26¾" H



2202 SZ
11" DIA., 19¼" H



2203 SZ
7" W, 9" H



2200 SZ
8½" W, 18" H



2206 SZ
7" W, 14" H



2204 SZ
10¾" W, 23¼" H



2207 SZ
11" DIA., 21¼" H



2201 SZ
13¾" DIA., 23¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2200 SZ	1-75w Med.	10¼"	11½"	5½" W, 5½" H Back Plate	
2201 SZ	4-40w Cand.			3" Dia. Post Fitter	
2202 SZ	1-100w Med.			5" Dia. Canopy	6', 5'
2203 SZ	1-60w Med.			5" Dia. Canopy	6', 5'
2204 SZ	1-100w Med.	13"	16"	4½" W, 9½" H Back Plate	
2205 SZ	1-100w Med.	15"	17¼"	4½" W, 10" H Back Plate	
2206 SZ	1-60w Med.	8"	9¼"	4¼" W, 5½" H Back Plate	
2207 SZ	3-40w Cand.			3" Dia. Post Fitter	

For posts and pier mounts, see pages 664-665. Ideal for vintage filament bulbs (not included).

SAYBROOK™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Saybrook's nautical-inspired design features a unique circular form of clear seedy glass bound by a dramatic floating center band fastened with cast knobs. The aluminum construction in a robust Oil Rubbed Bronze finish showcases the hand-applied highlights, adding an understated touch of British elegance and traditional detailing.



2342 OZ
11¼" DIA., 19¼" H



2340 OZ
7¼" W, 12" H



2344 OZ
9¼" W, 14¼" H



2345 OZ
11¼" W, 17½" H



2341 OZ
11¼" DIA., 18½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2340 OZ	1-100w Med.	8"	3"	5½" Dia. Back Plate	
2341 OZ	3-60w Cand.			3" Dia. Post Fitter	
2342 OZ	3-60w Cand.			5" Dia. Canopy	6', 5'
2344 OZ	1-100w Med.	8¼"	3¾"	5½" Dia. Back Plate	
2345 OZ	3-60w Cand.	11¼"	4½"	5½" Dia. Back Plate	

For posts and pier mounts, see pages 664-665.

Belden Place offers stylish simplicity with a dash of nautical elegance in durable solid aluminum construction. Its clean lines offer a modern take on a vintage gas lantern.

FINISH OIL RUBBED BRONZE
GLASS CLEAR

BELDEN PLACE™



2862 OZ
10" W, 16½" H
49" MAX. H*



2860 OZ
8" W, 11" H



2865 OZ
12" W, 19¼" H



2864 OZ
10" W, 16" H



2861 OZ
12" W, 22" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2860 OZ	1-100w Med.	9"	3¾"	4½" W, 7¼" H Back Plate		
2861 OZ	1-100w Med.			3" Dia. Post Fitter		
2862 OZ	1-100w Med.			6" Dia. Canopy	10'	1-6", 2-12"
2864 OZ	1-100w Med.	11"	4½"	4½" W, 7¼" H Back Plate		
2865 OZ	1-100w Med.	13"	4½"	4½" W, 7¼" H Back Plate		

*Maximum achievable height with stems included. Additional 12" stems available, 6061 OZOD. For posts and pier mounts, see pages 664-665. Ideal for vintage filament bulbs (not included).

TATUM™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Perfectly proportioned, Tatum's clean lines feature a hint of nautical nuance. A sturdy die cast housing with a bold decorative rim at the bottom edge in Oil Rubbed Bronze showcases the elegant clear seedy glass in an appealing vintage shape.



1884 OZ
8¼" W, 14¼" H



1880 OZ
5½" W, 9¾" H



1882 OZ
8¼" DIA., 16" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1880 OZ	1-100w Med.	6¼"	3½"	5" Dia. Back Plate	
1882 OZ	1-100w Med.			5½" Dia. Canopy	6', 5'
1884 OZ	1-100w Med.	8½"	4½"	5" W, 7" H Back Plate	

Ideal for vintage filament bulbs (not included).

Briggs is a beacon of style in this sea-worthy design. Discreet nautical elements complement the classic lines of a signal lantern to create a bold, clean silhouette.

FINISH BUCKEYE BRONZE
GLASS ETCHED SEEDY

BRIGGS™



2492 KZ
8¾" DIA., 18" H
51" MAX. H*



2494 KZ
8¾" W, 17¼" H



2495 KZ
10¼" W, 21" H



PIER MOUNT
2497 KZ
8¾" DIA., 15" H



2490 KZ
6½" W, 13½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
2490 KZ	1-100w Med.	7¼"	4¾"	4¼" W, 7¾" H Back Plate		
2492 KZ	1-100w Med.			6" Dia. Canopy	10'	1-6", 2-12"
2494 KZ	1-100w Med.	9½"	6¼"	4¼" W, 10" H Back Plate		
2495 KZ	1-100w Med.	11¼"	7"	5¼" W, 11½" H Back Plate		
2497 KZ	1-100w Med.			8" Dia. Base		

*Maximum achievable height with stems included. Additional 12" stems available, 6034 KZOD.

PORTER™

FINISH AGED ZINC
GLASS CLEAR

A fusion of chic styles makes Porter a design standout. Merging Modern Farmhouse, Industrial and Arts and Crafts elements, the fine rivet details and a sturdy hanger loop create a stunning and distinctive statement.



2805 DZ
7½" W, 25" H



2802 DZ
7½" W, 19" H



2804 DZ
6½" W, 22" H



2806 DZ
5½" W, 13" H



2800 DZ
6" W, 18½" H



2801 DZ
6½" W, 22¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2800 DZ	1-100w Med.*	7¼"	4½"	6" W, 9" H Back Plate	
2801 DZ	1-100w Med.*			3" Dia. Post Fitter	
2802 DZ	1-100w Med.*			5" Sq. Canopy	6', 5'
2804 DZ	1-100w Med.*	8¼"	4½"	6" W, 9" H Back Plate	
2805 DZ	1-100w Med.*	9¼"	4½"	6" W, 9" H Back Plate	
2806 DZ	1-100w Med.*	6½"	6½"	4½" W, 7" H Back Plate	

*Vintage filament 40w T bulb included. For posts and pier mounts, see pages 664-665.



Heritage
COLLECTION

HERITAGE

CLASSIC IS ALWAYS IN STYLE. EXPLORE THE HERITAGE COLLECTION: NINE FAMILIES OF TIMELESS LANTERN DESIGNS THAT PAY TRIBUTE TO AMERICA'S PAST AND HINKLEY'S 95-YEAR HISTORY.



AUTHENTIC APPEAL

Beginning as an outdoor lantern company in 1922, Hinkley has archives spanning nearly a century's worth of lighting designs. Inspired by these archives, the Heritage Collection is defined by enduring design elements such as:

- + Carriage-style silhouettes with hinged doors and rivet details
- + Gas lantern cage construction
- + An East Coast sense of style rich in colonial and nautical influence

ABOVE: THE ANCHORAGE + HARBOR COLLECTIONS | 1858DZ, PAGE 578 AND 1561SK,
SEE HINKLEYLIGHTING.COM. OPPOSITE PAGE: THE REVERE COLLECTION | 1185SN, PAGE 590

ADAIR™

FINISH AGED ZINC WITH
HERITAGE BRASS
GLASS CLEAR

Inspired by the early American coach lights popular throughout New England, Adair features a clean and stately form composed of hardy aluminum and brass. An Aged Zinc and Heritage Brass finish combination is complemented with robust construction details.

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.



2935 DZ
8½" W, 24½" H



2932 DZ
8½" W, 23" H



2930 DZ
7¼" W, 16½" H



2934 DZ
7¼" W, 20" H



2931 DZ
8½" W, 27¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2930 DZ	1-100w Med.	8½"	9¼"	4½" W, 6½" H Back Plate	
2931 DZ	3-60w Cand.			3" Dia. Post Fitter	
2932 DZ	3-60w Cand.			5" Square Canopy	6', 5'
2934 DZ	2-60w Cand.	8½"	9¼"	4½" W, 7" H Back Plate	
2935 DZ	3-60w Cand.	9¾"	10¼"	4½" W, 7½" H Back Plate	

Ideal for vintage filament bulbs (not included). For posts and pier mounts, see pages 664-665.

ANCHORAGE™

FINISH AGED ZINC
GLASS CLEAR

Anchorage is an early American lantern design crafted of solid aluminum to reflect a bold yet refined silhouette. The Aged Zinc finish and clear glass complement the long clean lines, elegant arched carriage handle and sturdy knobs, resulting in a vintage style with classic charisma.

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.

ADDITIONAL FINISHES
Light Oiled Bronze (LZ)



1858 DZ
1858 DZ-LL
13" W, 25" H





1852 DZ
1852 DZ-LL
11" W, 23¾" H



1854 DZ
1854 DZ-LL
9¼" W, 17¾" H



1850 DZ
7" W, 13" H



1855 DZ
1855 DZ-LL
11" W, 21¼" H



1851 DZ
1851 DZ-LL
11" W, 24¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1850 DZ	1-100w Med.			6"	7¾"	4½" W, 6" H Back Plate	
1851 DZ	3-60w Cand.	1851 DZ-LL	3-5w Cand. LED*			3" Dia. Post Fitter	
1852 DZ	3-60w Cand.	1852 DZ-LL	3-5w Cand. LED*			5¾" Dia. Canopy	6', 5'
1854 DZ	2-60w Cand.	1854 DZ-LL	2-5w Cand. LED*	7¾"	12½"	4½" W, 7" H Back Plate	
1855 DZ	3-60w Cand.	1855 DZ-LL	3-5w Cand. LED*	9"	15½"	4½" W, 7" H Back Plate	
1858 DZ	4-60w Cand.	1858 DZ-LL	4-5w Cand. LED*	10¾"	17½"	4½" W, 9" H Back Plate	

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

ANCHORAGE™

FINISH LIGHT OILED BRONZE
GLASS CLEAR

Anchorage is an early American lantern design crafted of solid aluminum to reflect a bold yet refined silhouette. The Light Oiled Bronze finish and clear glass complement the long clean lines, elegant arched carriage handle and sturdy knobs, resulting in a vintage style with classic charisma.

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.

ADDITIONAL FINISHES
Aged Zinc (DZ)



1858 LZ
1851 LZ-LL
13" W, 25" H





1852 LZ
1852 LZ-LL
11" W, 23¾" H



1854 LZ
1854 LZ-LL
9¼" W, 17¾" H



1850 LZ
7" W, 13" H



1855 LZ
1855 LZ-LL
11" W, 21¼" H



1851 LZ
1851 LZ-LL
11" W, 24¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1850 LZ	1-100w Med.			6"	7¾"	4½" W, 6" H Back Plate	
1851 LZ	3-60w Cand.	1851 LZ-LL	3-5w Cand. LED*			3" Dia. Post Fitter	
1852 LZ	3-60w Cand.	1852 LZ-LL	3-5w Cand. LED*			5¾" Dia. Canopy	6', 5'
1854 LZ	2-60w Cand.	1854 LZ-LL	2-5w Cand. LED*	7¾"	12½"	4½" W, 7" H Back Plate	
1855 LZ	3-60w Cand.	1855 LZ-LL	3-5w Cand. LED*	9"	15½"	4½" W, 7" H Back Plate	
1858 LZ	4-60w Cand.	1858 LZ-LL	4-5w Cand. LED*	10¾"	17½"	4½" W, 9" H Back Plate	

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

YORK™

FINISH BLACK
GLASS CLEAR SEEDY

York uses authentic exposed rivet construction hand-made in solid aluminum and celebrates the bold traditional lantern design Hinkley is renowned for. This classic hip roof and wire cage turn of the century style comes with an optional interior metallic reflector and rolled top loop. The gallant proportions of its striking silhouette are reinforced with a vintage Black finish, cast face plate and clear seedy glass.

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.



1845 BK
9½" W, 25" H



1842 BK
9½" W, 24½" H



1844 BK
7½" W, 21¼" H



1840 BK
5½" W, 15¼" H



1841 BK
9½" W, 28" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1840 BK	1-100w Med.	5¾"	11½"	5" Dia. Back Plate	
1841 BK	3-60w Cand.			3" Dia. Post Fitter	
1842 BK	3-60w Cand.			5" Dia. Canopy	6', 5'
1844 BK	2-60w Cand.	7½"	16"	5" Dia. Back Plate	
1845 BK	3-60w Cand.	9½"	18¾"	5" Dia. Back Plate	

For posts and pier mounts, see pages 664-665.

BINGHAM™

FINISH GREYSTONE
GLASS CLEAR SEEDY

Bingham's traditional style recalls a turn-of-the-century gas light reproduction. The vintage look is nautical in nature and recognizes Hinkley's origins on the shores of Lake Erie. The aluminum construction features clear seedy glass and a Greystone finish, while candelabra lamping completes the authentic style.

Heritage COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.

ADDITIONAL FINISHES
Sienna (SN)



2045 GS
2045 GS-LL
8" W, 21" H



INSTAFAVE



@smithteam6

THE BINGHAM COLLECTION



2044 GS
2044 GS-LL
6" W, 16" H

2040 GS
2040 GS-LL
4¾" W, 12½" H

2042 GS
2042 GS-LL
8" W, 23½" H

PIER MOUNT
2047 GS
2047 GS-LL
9¾" W, 21¼" H

2041 GS
2041 GS-LL
8" W, 23" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2040 GS	1-60w Cand.	2040 GS-LL	1-5w Cand. LED*	6½"	8"	4½" W, 7¼" H Back Plate	
2041 GS	3-60w Cand.	2041 GS-LL	3-5w Cand. LED*			3" Dia. Post Fitter	
2042 GS	3-60w Cand.	2042 GS-LL	3-5w Cand. LED*			5" Dia. Canopy	6', 5'
2044 GS	2-60w Cand.	2044 GS-LL	2-5w Cand. LED*	8"	10"	5¾" W, 9¼" H Back Plate	
2045 GS	3-60w Cand.	2045 GS-LL	3-5w Cand. LED*	10¼"	13¼"	7¼" W, 12" H Back Plate	
2047 GS	3-60w Cand.	2047 GS-LL	3-5w Cand. LED*			9¾" Square Base	

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

BINGHAM™

FINISH SIENNA
GLASS CLEAR SEEDY

Bingham's traditional style recalls a turn-of-the-century gas light reproduction. The vintage look is nautical in nature and recognizes Hinkley's origins on the shores of Lake Erie. The brass construction features clear seedy glass and a Sienna finish, while candelabra lamping completes the authentic style.

Heritage COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.

ADDITIONAL FINISHES
Greystone (GS)



2045 SN
2045 SN-LL
8" W, 21" H





ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2040 SN	1-60w Cand.	2040 SN-LL	1-5w Cand. LED*	6½"	8"	4½" W, 7¼" H Back Plate	
2041 SN	3-60w Cand.	2041 SN-LL	3-5w Cand. LED*			3" Dia. Post Fitter	
2042 SN	3-60w Cand.	2042 SN-LL	3-5w Cand. LED*			5" Dia. Canopy	6', 5'
2044 SN	2-60w Cand.	2044 SN-LL	2-5w Cand. LED*	8"	10"	5¾" W, 9¼" H Back Plate	
2045 SN	3-60w Cand.	2045 SN-LL	3-5w Cand. LED*	10¼"	13¼"	7¼" W, 12" H Back Plate	
2047 SN	3-60w Cand.	2047 SN-LL	3-5w Cand. LED*			9¾" Square Base	

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

NANTUCKET™

FINISH AGED BRASS
GLASS CLEAR SEEDY PANELS

A Hinkley classic, Nantucket features a timeless New England design for the ultimate in vintage nautical chic. An Aged Brass finish, clear seedy glass panels and durable solid brass construction add to its retro appeal.

Heritage COLLECTION

TIMELESS LANTERN DESIGNS THAT PAY TRIBUTE TO THE NOSTALGIA OF AMERICA'S PAST.



2370 AS
5½" W, 13½" H



2376 AS
4½" W, 9¾" H



2371 AS
7½" W, 20¾" H



2374 AS
6" W, 16¾" H



2372 AS
5½" W, 14½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2370 AS	1-75w Med.	5½"	9¼"	5½" W, 7" H Back Plate	
2371 AS	3-60w Cand.			3" Dia. Post Fitter	
2372 AS	2-40w Cand.			5" Dia. Canopy	6', 5'
2374 AS	2-60w Cand.	6¾"	11¼"	7½" W, 8¼" H Back Plate	
2376 AS	1-60w Med.	4½"	7"	4½" W, 5¼" H Back Plate	

For posts and pier mounts, see pages 664-665.

The classic sophistication of the Montauk collection brings together the finest elements of traditional East Coast style. The entire collection is made from solid brass, complemented by clear seedy glass and candelabra sockets for authentic appeal.

FINISH SIENNA
GLASS CLEAR SEEDY

MONTAUK™

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.



1202 SN
7" W, 17¼" H



1204 SN
7" W, 20¾" H



1200 SN
7" W, 17¼" H



1205 SN
9" W, 19½" H



1201 SN
9" W, 23¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1200 SN	2-60w Cand.	9¼"	10¼"	4½" W, 8" H Back Plate	
1201 SN	4-60w Cand.			3" Dia. Post Fitter	
1202 SN	2-60w Cand.			5" Dia. Canopy	6', 5'
1204 SN	3-60w Cand.	9¼"	10¼"	4½" W, 8" H Back Plate	
1205 SN	4-60w Cand.	11¼"	10½"	4½" W, 8" H Back Plate	

For posts and pier mounts, see pages 664-665.

REVERE™

FINISH SIENNA
GLASS CLEAR SEEDY

Revere is a classic, traditional coach lantern in solid brass with clear seedy glass panels. The glass faux candle sleeves complete the authentic appearance.

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.



1185 SN
7" W, 21¾" H

@INSTAFAVE



@curlsandcashmere
THE REVERE COLLECTION



1182 SN
7" W, 20½" H



1180 SN
4½" W, 17¼" H



1184 SN
7" W, 21¾" H



PIER MOUNT
1187 SN
9¾" W, 20¼" H



1181 SN
7" W, 22¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1180 SN	1-60w Cand.	5½"	10¼"	4½" W, 11" H Back Plate	
1181 SN	3-60w Cand.			3" Dia. Post Fitter	
1182 SN	3-60w Cand.			5" Dia. Canopy	6', 5'
1184 SN	2-60w Cand.	7¼"	12¼"	4½" W, 11" H Back Plate	
1185 SN	3-60w Cand.	10"	12¼"	4½" W, 11" H Back Plate	
1187 SN	3-60w Cand.			9¾" Square Base	

For posts and pier mounts, see pages 664-665.



Sedgwick's brass construction symbolizes the best of vintage Hinkley quality and style. This traditional tapered rectangular lantern features a charming hinged door with sliding latch for authentic appeal. The classic Sienna finish combines beautifully with generous panels of clear seedy glass and embodies the essence of historic New England architecture and sophistication.

FINISH SIENNA
GLASS CLEAR SEEDY

SEDGWICK™

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.



1772 SN
7" W, 18¾" H



1770 SN
4½" W, 14½" H



1774 SN
7" W, 19¾" H



1775 SN
7" W, 19¾" H



1771 SN
7" W, 22" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1770 SN	1-60w Cand.	6½"	9"	4½" W, 11½" H Back Plate	
1771 SN	3-60w Cand.			3" Dia. Post Fitter	
1772 SN	3-60w Cand.			5" Dia. Canopy	6', 5'
1774 SN	2-60w Cand.	6½"	14"	4½" W, 11½" H Back Plate	
1775 SN	3-60w Cand.	9½"	14"	4½" W, 11¾" H Back Plate	

For posts and pier mounts, see pages 664-665.

LINCOLN™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Lincoln defines classic design with authentic hinged doors and panels of clear seedy glass adding to the allure of this traditional cast aluminum lantern.

Heritage
COLLECTION

TIMELESS LANTERN DESIGNS THAT
PAY TRIBUTE TO THE NOSTALGIA OF
AMERICA'S PAST.



2465 OZ
10" W, 19" H



2462 OZ
8½" W, 16¾" H



2468 OZ
10" W, 23¼" H



2460 OZ
7½" W, 13¾" H



2464 OZ
8½" W, 16¾" H



2461 OZ
10" W, 21" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2460 OZ	1-100w Med.	8¾"	6½"	4½" W, 9" H Back Plate	
2461 OZ	3-60w Cand.			3" Dia. Post Fitter	
2462 OZ	2-60w Cand.			5" Dia. Canopy	6', 5'
2464 OZ	2-60w Cand.	10¼"	6¾"	4¾" W, 12¼" H Back Plate	
2465 OZ	3-60w Cand.	11¼"	9¼"	4¾" W, 12¼" H Back Plate	
2468 OZ	3-60w Cand.	11¼"	13½"	4¾" W, 12¼" H Back Plate	

For posts and pier mounts, see pages 664-665.

ALFORD PLACE™

FINISH OIL RUBBED BRONZE
GLASS CLEAR

The clean and classic design of Alford Place features a precision die-cast frame, hanging arm and top loop, paired with a sealed glass roof, providing excellent illumination from all sides.



2565 OZ
12" W, 20½" H



2562 OZ
12" W, 19½" H



2564 OZ
10" W, 17½" H



2560 OZ
8" W, 14" H



2561 OZ
10" W, 20¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2560 OZ	2-60w Cand.	9"	7"	4¾" W, 5½" H Back Plate	
2561 OZ	2-60w Cand.			3" Dia. Post Fitter	
2562 OZ	3-60w Cand.			5" Sq. Canopy	6', 5'
2564 OZ	2-60w Cand.	11¼"	8¼"	4¾" W, 6¾" H Back Plate	
2565 OZ	3-60w Cand.	13½"	9½"	5½" W, 8¼" H Back Plate	

For posts and pier mounts, see pages 664-665.

TRELLIS™

FINISH AGED ZINC
GLASS CLEAR

Trellis is a traditional European hanging wall lantern design in an Aged Zinc finish with clear glass or Regency Bronze with clear seeded glass. The large scroll arm detail, cast loop finial and true rivet detail create a refined elegance.

ADDITIONAL FINISHES
Regency Bronze (RB)



1435 DZ
1435 DZ-LL
11" W, 22¼" H





1429 DZ
1429 DZ-LL
9" W, 14¾" H
(can be used with 1433DZ-SCR)



1433 DZ
1433 DZ-LL
(1433DZ-SCR included)
29¾" W, 14¾" H



1433 DZ-SCR
13" W, 9" H



1438 DZ
1438 DZ-LL
13" W, 26¼" H



PIER MOUNT
1437 DZ
1437 DZ-LL
11" W, 19¾" H



1431 DZ
1431 DZ-LL
11" W, 21" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
1429 DZ	3-60w Cand.	1429 DZ-LL	3-5w Cand. LED*	11½"	8½"	4½" W, 7" H Back Plate
1431 DZ	3-60w Cand.	1431 DZ-LL	3-5w Cand. LED*			3" Dia. Post Fitter
1433 DZ	3-60w Cand.	1433 DZ-LL	3-5w Cand. LED*	11½"	7¾"	4½" W, 7" H Back Plate
1433 DZ-SCR						
1435 DZ	4-60w Cand.	1435 DZ-LL	4-5w Cand. LED*	16¼"	8"	4½" W, 10" H Back Plate
1437 DZ	4-60w Cand.	1437 DZ-LL	4-5w Cand. LED*			10¼" Sq. Base
1438 DZ	4-60w Cand.	1438 DZ-LL	4-5w Cand. LED*	19"	9½"	5" W, 13" H Back Plate

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.



1432 DZ
1432 DZ-LL
11" W, 23¼" H



1428 DZ
1428 DZ-LL
16" W, 31¼" H



1430 DZ
7" W, 15¼" H



1434 DZ
1434 DZ-LL
9" W, 19¾" H



1436 DZ
1436 DZ-LL
11" W, 35¾" H



1439 DZ
1439 DZ-LL
16" W, 52" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1428 DZ	4-60w Cand.	1428 DZ-LL	4-5w Cand. LED*			6" Square Canopy	12', 10'
1430 DZ	1-100w Med.			11¼"	6"	4½" W, 7" H Back Plate	
1432 DZ	3-60w Cand.	1432 DZ-LL	3-5w Cand. LED*			4½" Square Canopy	6', 5'
1434 DZ	3-60w Cand.	1434 DZ-LL	3-5w Cand. LED*	14¼"	8"	4½" W, 10" H Back Plate	
1436 DZ	4-60w Cand.	1436 DZ-LL	4-5w Cand. LED*	16½"	17¾"	4½" W, 13" H Back Plate	
1439 DZ	4-60w Cand.	1439 DZ-LL	4-5w Cand. LED*	24"	27½"	4¾" W, 20" H Back Plate	

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com.

Trellis is a traditional European hanging wall lantern design in an Aged Zinc finish with clear glass or Regency Bronze with clear seedy glass. The large scroll arm detail, cast loop finial and true rivet detail create a refined elegance.

FINISH REGENCY BRONZE
GLASS CLEAR SEEDY

TRELLIS™

ADDITIONAL FINISHES
Aged Zinc (DZ)



1435 RB
1435 RB-LL
11" W, 22¼" H





1433 RB
1433 RB-LL
(1433RB-SCR included)
29¾" W, 14¾" H



1429 RB
1429 RB-LL
9" W, 14¾" H
(can be used with 1433RB-SCR)



1433 RB-SCR
13" W, 9" H



1431 RB
1431 RB-LL
11" W, 21" H



PIER MOUNT
1437 RB
1437 RB-LL
11" W, 19¾" H



1438 RB
1438 RB-LL
13" W, 26¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
1429 RB	3-60w Cand.	1429 RB-LL	3-5w Cand. LED*	11½"	8½"	4½" W, 10" H Back Plate
1431 RB	3-60w Cand.	1431 RB-LL	3-5w Cand. LED*			3" Dia. Post Fitter
1433 RB	3-60w Cand.	1433 RB-LL	3-5w Cand. LED*	11½"	8½"	4½" W, 10" H Back Plate
1433 RB-SCR						
1435 RB	4-60w Cand.	1435 RB-LL	4-5w Cand. LED*	16½"	8"	4½" W, 10" H Back Plate
1437 RB	4-60w Cand.	1437 RB-LL	4-5w Cand. LED*			10¼" Square Base
1438 RB	4-60w Cand.	1438 RB-LL	4-5w Cand. LED*	19"	9½"	5" W, 13" H Back Plate

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.



1430 RB
7" W, 15¼" H



1428 RB
1428 RB-LL
16" W, 31¼" H



1432 RB
1432 RB-LL
11" W, 23¼" H



1439 RB
1439 RB-LL
16" W, 52" H



1436 RB
1436 RB-LL
11" W, 35¼" H



1434 RB
1434 RB-LL
9" W, 19¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1428 RB	4-60w Cand.	1428 RB-LL	4-5w Cand. LED*			6" Square Canopy	12', 10'
1430 RB	1-100w Med.			11¼"	6"	4½" W, 7" H Back Plate	
1432 RB	3-60w Cand.	1432 RB-LL	3-5w Cand. LED*			4½" Square Canopy	6', 5'
1434 RB	3-60w Cand.	1434 RB-LL	3-5w Cand. LED*	14¼"	8"	4½" W, 10" H Back Plate	
1436 RB	4-60w Cand.	1436 RB-LL	4-5w Cand. LED*	16½"	17¾"	4½" W, 13" H Back Plate	
1439 RB	4-60w Cand.	1439 RB-LL	4-5w Cand. LED*	24"	27½"	4¾" W, 20" H Back Plate	

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com.

BROMLEY™

FINISH MUSEUM BLACK
GLASS CLEAR

Bromley's handsome silhouette features an updated traditional design that combines elegant and stately details. These dignified die-casted aluminum fixtures convey sophistication in a Museum Black finish that complements any façade. Specialty touches such as a "Shepard's Hook" decorative scrolled arm and multiple mounting points highlight Bromley's homage to tradition and quality.

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



2366 MB
10" W, 24¾" H



2362 MB
10" W, 19¼" H



2364 MB
8" W, 20" H



2360 MB
8" W, 15½" H



2368 MB
8" W, 11¾" H



2365 MB
10" W, 19¼" H



2361 MB
10" W, 22¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2360 MB	2-60w Cand.	9¼"	7½"	4¾" W, 8½" H Back Plate	
2361 MB	3-60w Cand.			3" Dia. Post Fitter	
2362 MB	3-60w Cand.			5¼" Dia. Canopy	6', 5'
2364 MB	2-60w Cand.	9¾"	12¾"	4¾" W, 8½" H Back Plate	
2365 MB	3-60w Cand.	11¼"	8½"	4¾" W, 8½" H Back Plate	
2366 MB	3-60w Cand.	11¾"	16¾"	4¾" W, 8½" H Back Plate	
2368 MB	1-100w Med.	9¼"	7½"	4¾" W, 8¼" H Back Plate	

For posts and pier mounts, see pages 664-665.

BROMLEY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR

Bromley's handsome silhouette features an updated traditional design that combines elegant and stately details. These dignified die-casted aluminum fixtures convey sophistication in an Oil Rubbed Bronze finish that complements any façade. Specialty touches such as a "Shepard's Hook" decorative scrolled arm and multiple mounting points highlight Bromley's homage to tradition and quality.

ADDITIONAL FINISHES
Museum Black (MB)



2366 OZ
10" W, 24¾" H



2362 OZ
10" W, 19¼" H



2364 OZ
8" W, 20" H



2360 OZ
8" W, 15½" H



2368 OZ
8" W, 11¾" H



2365 OZ
10" W, 19¼" H



2361 OZ
10" W, 22¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2360 OZ	2-60w Cand.	9¼"	7½"	4¾" W, 8½" H Back Plate	
2361 OZ	3-60w Cand.			3" Dia. Post Fitter	
2362 OZ	3-60w Cand.			5¼" Square Canopy	6', 5'
2364 OZ	2-60w Cand.	9¾"	12¾"	4¾" W, 8½" H Back Plate	
2365 OZ	3-60w Cand.	11¼"	8½"	4¾" W, 8½" H Back Plate	
2366 OZ	3-60w Cand.	11¾"	16¾"	4¾" W, 8½" H Back Plate	
2368 OZ	1-100w Med.	9¼"	7½"	4¾" W, 8¼" H Back Plate	

For posts and pier mounts, see pages 664-665.

ENZO™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY

Enzo blends delicate beauty and lasting durability. The intricate die cast aluminum construction features graceful scrolls with Old World allure. An Oil Rubbed Bronze finish combines with clear seedy glass for timeless elegance.



2275 OZ
10" W, 18¾" H



2272 OZ
10" W, 19" H



2278 OZ
10" W, 28½" H



2274 OZ
8" W, 15¼" H



2271 OZ
10" W, 21" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2271 OZ	1-100w Med.			3" Dia. Post Fitter	
2272 OZ	1-100w Med.			5" Square Canopy	6', 5'
2274 OZ	1-100w Med.	9½"	6"	5" W, 15" H Back Plate	
2275 OZ	1-100w Med.	11½"	7"	5¼" W, 18½" H Back Plate	
2278 OZ	1-100w Med.	11¾"	14½"	5¼" W, 18½" H Back Plate	

For posts and pier mounts, see pages 664-665.

BOLLA™

FINISH OLDE BRONZE
GLASS CLEAR SEEDY

The graceful lines of Bolla create a soft elegance, while the solid brass construction and heavy cast ball transitions add to its innovative style.

ADDITIONAL FINISHES

Olde Bronze with Light Amber Seedy Glass (OB)



2649 OB
14" W, 26" H



2642 OB
11" DIA., 20½" H



2643 OB
16¾" DIA., 8" H



2644 OB
9" W, 15¾" H



2645 OB
11" W, 18¾" H



2646 OB
6" W, 11" H



2640 OB
7¼" W, 12¼" H



2641 OB
11" DIA., 20½" H
(shown as pier mount
with 1304 OB)*

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2640 OB	1-60w Med.	9"	7"	4½" W, 7¼" H Back Plate	
2641 OB	3-40w Cand.			3" Dia. Post Fitter	
2642 OB	3-40w Cand.			5" Dia. Canopy	6', 5'
2643 OB	2-75w Med.				
2644 OB	2-40w Cand.	10½"	8"	4½" W, 7¼" H Back Plate	
2645 OB	3-40w Cand.	12½"	9¾"	4½" W, 9" H Back Plate	
2646 OB	1-60w Med.	6¾"	3"	5" W, 6" H Back Plate	
2649 OB	4-40w Cand.	16"	12¾"	4½" W, 11½" H Back Plate	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

BOLLA™

FINISH OLDE BRONZE
GLASS LIGHT AMBER SEEDY

The graceful lines of Bolla create a soft elegance, while the solid brass construction and heavy cast ball transitions add to its innovative style.

ADDITIONAL FINISHES

Olde Bronze with Clear Seedy Glass (OB)



2639 OB
2639 OB-LED
14" W, 26" H





2632 OB
2632 OB-LED
11" DIA., 20½" H
T24



2633 OB
2633 OB-LED
16¾" DIA., 8" H
T24



2634 OB
2634 OB-LED
9" W, 15¾" H
T24



2635 OB
2635 OB-LED
11" W, 18¾" H
T24



2636 OB
2636 OB-LED
6" W, 11" H
T24



2630 OB
2630 OB-LED
7¼" W, 12¼" H
T24



2631 OB
2631 OB-LED
11" DIA., 20½" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2630 OB	1-60w Med.	2630 OB-LED	15w LED	1100	2700K	92	1-75w	9"	7"	4½" W, 7¼" H Back Plate	
2631 OB	3-40w Cand.	2631 OB-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
2632 OB	3-40w Cand.	2632 OB-LED	15w LED	1100	2700K	92	1-75w			5" Dia. Canopy	6', 5'
2633 OB	2-75w Med.	2633 OB-LED	32w LED	2300	2700K	96	2-100w				
2634 OB	2-40w Cand.	2634 OB-LED	15w LED	1100	2700K	92	1-75w	10½"	8"	4½" W, 7¼" H Back Plate	
2635 OB	3-40w Cand.	2635 OB-LED	15w LED	1100	2700K	92	1-75w	12½"	9¾"	4½" W, 9" H Back Plate	
2636 OB	1-60w Med.	2636 OB-LED	15w LED	1100	2700K	92	1-75w	6¾"	3"	5" W, 6" H Back Plate	
2639 OB	4-40w Cand.	2639 OB-LED	15w LED	1100	2700K	92	1-75w	16"	12¾"	4½" W, 11½" H Back Plate	

For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

CASA™

FINISH OLDE BLACK
GLASS CLEAR SEEDY

Casa features solid aluminum construction with twisted wrought iron details and hand-forged scrollwork in an Olde Black finish to complete its rustic-chic appeal with a Southwestern flair.

ADDITIONAL FINISHES

Olde Black with Light Etched Amber Glass (OL)



1144 OL-CL
9¾" W, 17½" H



1147 OL-CL
12" DIA., 23¾" H



1140 OL-CL
7" W, 13" H



1143 OL-CL
9¾" W, 21½" H



1148 OL-CL
12" W, 26" H



1141 OL-CL
12" DIA., 23¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1140 OL-CL	1-60w Med.	7¾"	7"	4½" W, 7" H Back Plate	
1141 OL-CL	3-60w Cand.			3" Dia. Post Fitter	
1143 OL-CL	2-60w Cand.	9½"	9¾"	4½" W, 9" H Back Plate	
1144 OL-CL	1-75w Med.	9½"	9¾"	4½" W, 9" H Back Plate	
1147 OL-CL	3-60w Cand.			5½" Dia. Canopy	6', 5'
1148 OL-CL	3-60w Cand.	11¼"	10¾"	4½" W, 9" H Back Plate	

For posts and pier mounts, see pages 664-665.

CASA™

FINISH OLDE BLACK
GLASS LIGHT ETCHED AMBER

Casa features solid aluminum construction with twisted wrought iron details and hand-forged scrollwork in an Olde Black finish to complete its rustic-chic appeal with a Southwestern flair.

ADDITIONAL FINISHES

Olde Black with Clear Seedy Glass (OL-CL)



1145 OL
12" W, 20¾" H



1142 OL
12" DIA., 18" H



1144 OL
9¾" W, 17½" H



1140 OL
7" W, 13" H



1141 OL
12" DIA., 23¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1140 OL	1-60w Med.	7¾"	7"	4½" W, 7" H Back Plate	
1141 OL	3-60w Cand.			3" Dia. Post Fitter	
1142 OL	1-100w Med.			5½" Dia. Canopy	6', 5'
1144 OL	1-75w Med.	9½"	9¾"	4½" W, 9" H Back Plate	
1145 OL	1-100w Med.	11¼"	10¾"	4½" W, 9" H Back Plate	

For posts and pier mounts, see pages 664-665.

SORRENTO™

FINISH AGED IRON
 GLASS CLEAR SEEDY
 (OUTER GLASS), OPTIC ETCHED
 AMBER (INNER GLASS)

Sorrento's cast aluminum construction and flourishing cast details are enhanced by its hand-applied Aged Iron finish with copper highlights. Stunning optic etched amber inner glass is surrounded by panels of clear seedy outer glass, creating a grand statement.



1424 AI
 9¾" W, 20½" H



1420 AI
 8" W, 17" H



1421 AI
 12¼" W, 28¾" H



1425 AI
 12¼" W, 26¾" H



1422 AI
 12¼" W, 24" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE	WIRE/ CHAIN
1420 AI	1-100w Med.	11½"	10"	5" W, 9" H Back Plate	
1421 AI	1-100w Med.			3" Dia. Post Fitter	
1422 AI	1-100w Med.			5½" Dia. Canopy	6', 5'
1424 AI	1-100w Med.	13½"	12"	5" W, 9" H Back Plate	
1425 AI	1-100w Med.	16½"	16½"	5" W, 13" H Back Plate	

For posts and pier mounts, see pages 664-665.

Gorgeous details add drama to Brynmar's classic cast aluminum design. The decorative cast leaf and cross-hatch detailing in a Regency Bronze finish complement the stylish amber linen glass.

FINISH REGENCY BRONZE
GLASS AMBER LINEN

BRYNMAR™



ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1930 RB	1-60w Med.	8"	4"	4¾" W, 7" H Back Plate	
1931 RB	1-100w Med.			3" Dia. Post Fitter	
1932 RB	1-100w Med.			5½" Dia. Canopy	6', 5'
1934 RB	1-75w Med.	10½"	10¾"	4¾" W, 14" H Back Plate	
1935 RB	1-100w Med.	12¾"	14"	4¾" W, 18" H Back Plate	
1936 RB	1-60w Med.	6"	3¼"	4¾" W, 6" H Back Plate	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

PLANTATION™

FINISH PEARL BRONZE
GLASS INSIDE ETCHED
AMBER OPTIC

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped optic glass, durable brass and aluminum construction and elaborate, decorative cast detailing to create a noble statement.

ADDITIONAL FINISHES
Copper Bronze (CB)



2124 PZ
10¼" W, 28" H



2122 PZ
12½" DIA., 28½" H



2123 PZ
16" DIA., 8¾" H



2128 PZ
12" DIA., 8" H



2126 PZ
6" W, 14" H



2120 PZ
8" W, 21¼" H



2121 PZ
10¼" DIA., 25¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2120 PZ	1-75w Med.	11"	11"	5" W, 16" H Back Plate	
2121 PZ	1-100w Med.			3" Dia. Post Fitter	
2122 PZ	1-100w Med.			6¾" Dia. Canopy	6', 5'
2123 PZ	3-60w Med.				
2124 PZ	1-75w Med.	13¾"	14½"	5" W, 20" H Back Plate	
2126 PZ	1-60w Med.	7"	5"	5" W, 8" H Back Plate	
2128 PZ	2-60w Med.				

For posts and pier mounts, see pages 664-665.

PLANTATION™

FINISH COPPER BRONZE
GLASS CLEAR OPTIC

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped optic glass, durable brass and aluminum construction and elaborate, decorative cast detailing to create a noble statement.

ADDITIONAL FINISHES
Pearl Bronze (PZ)



2225 CB
12½" W, 34¼" H



2222 CB
12½" DIA., 28½" H



4881 CB
16" DIA., 8¾" H



4102 CB
12" DIA., 8" H



2224 CB
10¼" W, 28" H



2220 CB
8" W, 21¼" H



2226 CB
6" W, 14" H



2221 CB
10¼" DIA., 25¼" H
(shown as
pier mount with
1304 CB)*



2227 CB
12½" DIA., 29½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2220 CB	1-75w Med.	11"	11"	5" W, 16" H Back Plate	
2221 CB	3-40w Cand.			3" Dia. Post Fitter	
2222 CB	4-40w Cand.			6" Dia. Canopy	6', 5'
2224 CB	3-40w Cand.	13¾"	14½"	5" W, 20" H Back Plate	
2225 CB	4-40w Cand.	17¼"	17¼"	5" W, 24" H Back Plate	
2226 CB	1-60w Med.	7"	5"	5" W, 8" H Back Plate	
2227 CB	4-40w Cand.			3" Dia. Post Fitter	
4102 CB	2-60w Med.				
4881 CB	3-60w Med.				

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

WESTWINDS™

FINISH SIENNA

GLASS CLEAR WATER GLASS PANELS

Westwinds features intricate stamped filigree detailing in a classic Sienna finish. The durable solid brass construction and clear water glass panels impart an authentic, timeless feel.



2996 SN
12³/₄" W, 28" H



2992 SN
10½" W, 16¼" H



2995 SN
10½" W, 22½" H



2989 SN
6" W, 11¾" H



2990 SN
8¼" W, 19½" H



2991 SN
12¾" W, 20½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2989 SN	1-60w Med.	6½"	8"	4¾" W, 5½" H Back Plate	
2990 SN	2-40w Cand.	9¾"	13¾"	4½" W, 9½" H Back Plate	
2991 SN	3-40w Cand.			3" Dia. Post Fitter	
2992 SN	3-40w Cand.			5½" Dia. Canopy	6', 5'
2995 SN	3-40w Cand.	12½"	17½"	4½" W, 9½" H Back Plate	
2996 SN	3-40w Cand.	14½"	21½"	4¾" W, 12¼" H Back Plate	

For posts and pier mounts, see pages 664-665.



"The modern market offers up a wealth of durable, stain-resistant fabrics that are not only sturdy, but stylish, and we love combining those with weather-resistant lanterns and furnishings in natural finishes to create peaceful, resort-inspired spaces."



MARIE FLANIGAN
MARIE FLANIGAN INTERIORS
HOUSTON, TX

ABOVE: THE BARRINGTON COLLECTION | 1752VZ, PAGE 627

Barrington's chic, classic style transforms this design into a modern interpretation of the traditional outdoor lantern, constructed of solid aluminum. The cast finials combine with the clear seedy glass for added authenticity, while the lustrous finish is created in a multi-step, hand-painted process.

FINISH VICTORIAN BRONZE
GLASS CLEAR SEEDY

BARRINGTON™



1752 VZ
9" DIA., 24¼" H



1754 VZ
9" W, 22½" H



1750 VZ
7½" W, 20¼" H



1751 VZ
9" DIA., 23¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1750 VZ	3-60w Cand.	10½"	10¼"	4½" W, 11½" H Back Plate	
1751 VZ	4-60w Cand.			3" Dia. Post Fitter	
1752 VZ	4-60w Cand.			5¾" Dia. Canopy	6', 5'
1754 VZ	4-60w Cand.	12½"	11¼"	4½" W, 11½" H Back Plate	

For posts and pier mounts, see pages 664-665.

RALEY™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY GLASS PANELS

Raley's regal appearance features cast aluminum construction, a bold Oil Rubbed Bronze finish, flourishing details and clear water glass panels for a dignified style statement.

ADDITIONAL FINISHES
Museum Black (MB)



1609 OZ
1609 OZ-LL
13" W, 41¼" H





1602 OZ
1602 OZ-LL
11¾" DIA., 27½" H



1600 OZ
7¼" W, 16¾" H



1604 OZ
1604 OZ-LL
9½" W, 25¾" H



1605 OZ
1605 OZ-LL
11¾" W, 31½" H



1601 OZ
1601 OZ-LL
11¾" DIA., 26¼" H
(shown as pier mount
with 1304 OZ)**



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1600 OZ	1-60w Med.			9½"	10¼"	4½" W, 7½" H Back Plate	
1601 OZ	4-40w Cand.	1601 OZ-LL	4-5w Cand. LED*			3" Dia. Post Fitter	
1602 OZ	4-40w Cand.	1602 OZ-LL	4-5w Cand. LED*			5½" Dia. Canopy	6', 5'
1604 OZ	3-40w Cand.	1604 OZ-LL	3-5w Cand. LED*	12¼"	13¾"	4½" W, 9¼" H Back Plate	
1605 OZ	4-40w Cand.	1605 OZ-LL	4-5w Cand. LED*	14¾"	15¾"	4½" W, 9¼" H Back Plate	
1609 OZ	4-40w Cand.	1609 OZ-LL	4-5w Cand. LED*	17¼"	20¾"	5½" W, 18" H Back Plate	

*LED filament bulb included, see page 7. **Not for use within 4 ft. of ground. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

RALEY™

FINISH MUSEUM BLACK
GLASS CLEAR WATER GLASS PANELS

Raley's regal appearance features cast aluminum construction, a bold Museum Black finish, flourishing details and clear water glass panels for a dignified style statement.

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



1609 MB
1609 MB-LL
13" W, 41¼" H





1602 MB
1602 MB-LL
11¾" DIA., 27½" H



1600 MB
7¼" W, 16¾" H



1604 MB
1604 MB-LL
9½" W, 25¾" H



1605 MB
1605 MB-LL
11¾" W, 31½" H



1601 MB
1601 MB-LL
11¾" DIA., 26¼" H



ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1600 MB	1-60w Med.			9½"	10¼"	4½" W, 7½" H Back Plate	
1601 MB	4-40w Cand.	1601 MB-LL	4-5w Cand. LED*			3" Dia. Post Fitter	
1602 MB	4-40w Cand.	1602 MB-LL	4-5w Cand. LED*			5½" Dia. Canopy	6', 5'
1604 MB	3-40w Cand.	1604 MB-LL	3-5w Cand. LED*	12¼"	13¾"	4½" W, 9¼" H Back Plate	
1605 MB	4-40w Cand.	1605 MB-LL	4-5w Cand. LED*	14¾"	15¾"	4½" W, 9¼" H Back Plate	
1609 MB	4-40w Cand.	1609 MB-LL	4-5w Cand. LED*	17¼"	20¾"	5½" W, 18" H Back Plate	

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

WINDSOR™

FINISH BLACK
GLASS CLEAR WATER GLASS

Windsor combines elegant details and decorative cast detailing into its cast aluminum construction. The Black finish and clear water glass add to its majestic style.

ADDITIONAL FINISHES
River Rock (RK)



1929 BK
1929 BK-LED
14" W, 42" H





1892 BK
1892 BK-LED
12½" DIA., 28½" H
T24



1895 BK
1895 BK-LED
12½" W, 32" H
T24



1890 BK
1890 BK-LED
7" W, 12½" H
T24



1894 BK
1894 BK-LED
9½" W, 25½" H
T24



1898 BK
1898 BK-LED
9½" W, 20¾" H
T24



1899 BK
1899 BK-LED
12½" W, 25¾" H
T24



1921 BK
1921 BK-LED
14¼" DIA., 34¾" H
T24



1891 BK
1891 BK-LED
12½" DIA., 30" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1890 BK	1-75w Med.	1890 BK-LED	15w LED	1100	2700K	92	1-75w	8¼"	5"	5¾" W, 8" H Back Plate	
1891 BK	4-40w Cand.	1891 BK-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1892 BK	4-40w Cand.	1892 BK-LED	30w LED	2200	2700K	92	2-75w			5½" Dia. Canopy	6', 5'
1894 BK	3-40w Cand.	1894 BK-LED	15w LED	1100	2700K	92	1-75w	12"	13"	5¾" W, 12" H Back Plate	
1895 BK	4-40w Cand.	1895 BK-LED	15w LED	1100	2700K	92	1-75w	15½"	16½"	6¼" W, 15" H Back Plate	
1898 BK	3-40w Cand.	1898 BK-LED	15w LED	1100	2700K	92	1-75w	12"	12½"	5¾" W, 12" H Back Plate	
1899 BK	4-40w Cand.	1899 BK-LED	15w LED	800	2700K	96	1-75w	15½"	15¼"	6¼" W, 15" H Back Plate	
1921 BK	6-40w Cand.	1921 BK-LED	30w LED	2200	2700K	92	2-75w			3" Dia. Post Fitter	
1929 BK	6-40w Cand.	1929 BK-LED	30w LED	2200	2700K	92	2-75w	17"	19½"	6¼" W, 17" H Back Plate	

For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

WINDSOR™

FINISH RIVER ROCK
GLASS CLEAR WATER GLASS

Windsor combines elegant details and decorative cast detailing into its cast aluminum construction. The River Rock finish and clear water glass add to its majestic style.

ADDITIONAL FINISHES
Black (BK)



1929 RK
1929 RK-LED
14" W, 42" H





1892 RK
1892 RK-LED
12½" DIA., 28½" H
T24



1895 RK
1895 RK-LED
12½" W, 32" H
T24



1890 RK
1890 RK-LED
7" W, 12½" H
T24



1894 RK
1894 RK-LED
9½" W, 25½" H
T24



1898 RK
1898 RK-LED
9½" W, 20¾" H
T24



1899 RK
1899 RK-LED
12½" W, 25¾" H
T24



1921 RK
1921 RK-LED
14¼" DIA., 34¾" H
T24



1891 RK
1891 RK-LED
12½" DIA., 30" H
T24

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCAN. EQUIV.	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
1890 RK	1-75w Med.	1890 RK-LED	15w LED	1100	2700K	92	1-75w	8¼"	5"	5¾" W, 8" H Back Plate	
1891 RK	4-40w Cand.	1891 RK-LED	15w LED	1100	2700K	92	1-75w			3" Dia. Post Fitter	
1892 RK	4-40w Cand.	1892 RK-LED	30w LED	2200	2700K	92	2-75w			5½" Dia. Canopy	6', 5'
1894 RK	3-40w Cand.	1894 RK-LED	15w LED	1100	2700K	92	1-75w	12"	13"	5¾" W, 12" H Back Plate	
1895 RK	4-40w Cand.	1895 RK-LED	15w LED	1100	2700K	92	1-75w	15½"	16½"	6¼" W, 15" H Back Plate	
1898 RK	3-40w Cand.	1898 RK-LED	15w LED	1100	2700K	92	1-75w	12"	12½"	5¾" W, 12" H Back Plate	
1899 RK	4-40w Cand.	1899 RK-LED	15w LED	800	2700K	96	1-75w	15½"	15¼"	6¼" W, 15" H Back Plate	
1921 RK	6-40w Cand.	1921 RK-LED	30w LED	2200	2700K	92	2-75w			3" Dia. Post Fitter	
1929 RK	6-40w Cand.	1929 RK-LED	30w LED	2200	2700K	92	2-75w	17"	19½"	6¼" W, 17" H Back Plate	

For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

OXFORD™

FINISH MIDNIGHT BRONZE
GLASS CLEAR OPTIC

Oxford's sophisticated silhouette features solid aluminum construction with bead detailing in a Midnight Bronze finish, complemented by clear optic glass for a chic yet classic style statement.



1245 MN
12" W, 28½" H



1242 MN
12" DIA., 27½" H



1240 MN
7" W, 17¼" H



1243 MN
16¼" DIA., 7½" H



1244 MN
9¾" W, 23½" H



1241 MN
12" DIA., 28¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1240 MN	1-60w Med.	9"	10"	4¾" W, 9" H Back Plate	
1241 MN	3-40w Cand.			3" Dia. Post Fitter	
1242 MN	3-40w Cand.			6¾" Dia. Canopy	6', 5'
1243 MN	2-60w Med.				
1244 MN	3-40w Cand.	12¼"	12½"	4¾" W, 9" H Back Plate	
1245 MN	3-40w Cand.	15"	16¼"	4¾" W, 16" H Back Plate	

For posts and pier mounts, see pages 664-665.

TRAFALGAR™

FINISH MOCHA
GLASS CLEAR SEEDY

Trafalgar's grand design in sturdy cast aluminum adds historical flair with delicate scroll arch detail, authentic distressed finish and clear seedy glass.

ADDITIONAL FINISHES
Museum Black (MB)



1311 MO
12" W, 27½" H

1317 MO
8" W, 19" H

1314 MO
8" W, 17½" H

1315 MO
10" W, 22" H

1312 MO
12" W, 25" H

1319 MO
12" W, 26½" H

1316 MO
6" W, 10¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1311 MO	3-40w Cand.			3" Dia. Post Fitter	
1312 MO	3-40w Cand.			5" Square Canopy	6', 5'
1314 MO	1-75w Med.	10½"	7½"	6¾" W, 12½" H Back Plate	
1315 MO	3-40w Cand.	13½"	9½"	8½" W, 15½" H Back Plate	
1316 MO	1-60w Med.	7½"	5¼"	4½" W, 7" H Back Plate	
1317 MO	1-100w Med.			3" Dia. Post Fitter	
1319 MO	3-40w Cand.	16"	11½"	10" W, 18¾" H Back Plate	

For posts and pier mounts, see pages 664-665.

Trafalgar's grand design in sturdy cast aluminum adds historical flair with delicate scroll arch detail, authentic distressed finish and clear seeded glass.

FINISH MUSEUM BLACK
GLASS CLEAR SEEDY

TRAFALGAR™

ADDITIONAL FINISHES
Mocha (MO)



1312 MB
12" W, 25" H



1315 MB
10" W, 22" H



1314 MB
8" W, 17½" H



1316 MB
6" W, 10¼" H



1319 MB
12" W, 26½" H



1317 MB
8" W, 19" H
(shown as
pier mount with
1304 MB)*



1311 MB
12" W, 27½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1311 MB	3-40w Cand.			3" Dia. Post Fitter	
1312 MB	3-40w Cand.			5" Square Canopy	6', 5'
1314 MB	1-75w Med.	10½"	7½"	6¾" W, 12½" H Back Plate	
1315 MB	3-40w Cand.	13½"	9½"	8½" W, 15½" H Back Plate	
1316 MB	1-60w Med.	7½"	5¼"	4½" W, 7" H Back Plate	
1317 MB	1-100w Med.			3" Dia. Post Fitter	
1319 MB	3-40w Cand.	16"	11½"	10" W, 18¾" H Back Plate	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

WABASH™

FINISH MUSEUM BLACK
GLASS CLEAR BEVELED WITH
ETCHED GLASS CORNER PANELS

Wabash features solid aluminum construction with clear beveled glass, etched glass corner panels and decorative chevron detailing in a distressed finish.



1336 MB
6¼" W, 10½" H



1334 MB
8¼" W, 13¾" H



1331 MB
11" W, 23" H



1335 MB
11" W, 18½" H



1332 MB
11" W, 17¾" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1331 MB	3-40w Cand.			3" Dia. Post Fitter	
1332 MB	3-40w Cand.			4¾" Square Canopy	6', 5'
1334 MB	2-40w Cand.	10"	4¼"	5½" W, 9" H Back Plate	
1335 MB	3-40w Cand.	13¾"	5¼"	5½" W, 11¾" H Back Plate	
1336 MB	1-60w Med.	7¾"	4"	4½" W, 6¾" H Back Plate	

For posts and pier mounts, see pages 664-665.

Senator's stately cast aluminum and brass design features a striking Black finish with crisp panels of beveled, bound glass.

FINISH BLACK
GLASS CLEAR BOUND AND
BEVELED

SENATOR™



2502 BK
12¾" W, 25½" H



2505 BK
12¾" W, 26" H



2500 BK
8½" W, 13¾" H



2504 BK
11" W, 21¾" H



2501 BK
12¾" DIA., 26½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2500 BK	1-60w Med.	9"	6½"	5" W, 6¾" H Back Plate	
2501 BK	3-40w Cand.			3" Dia. Post Fitter	
2502 BK	3-40w Cand.			5" Dia. Canopy	6', 5'
2504 BK	3-40w Cand.	11½"	7¾"	5" W, 6¾" H Back Plate	
2505 BK	3-40w Cand.	15"	10"	6½" W, 8¾" H Back Plate	

For posts and pier mounts, see pages 664-665.

MANOR HOUSE™

FINISH BLACK
GLASS CLEAR BEVELED PANELS

Manor House is a classic lantern design featuring durable cast aluminum, clear beveled glass panels and a bold Black finish. Select-A-Lite options come standard with both candelabra and medium based sockets.



1819 BK
7" W, 12½" H



1445 BK
36" W, 22¾" H



1471 BK
13¾" W, 27½" H



1441 BK
10½" W, 22" H



1412 BK
8¾" W, 15" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
1412 BK	1-60w Med.			5½" Dia. Canopy	6', 5'
1441 BK	3-25w Cand. or 1-75w Med.			3" Dia. Post Fitter	
1445 BK	3-25w Cand. or 1-75w Med.	13"	14½"	5" W, 8¼" H Back Plate	
1471 BK	3-40w Cand. or 1-100w Med.			3" Dia. Post Fitter	
1819 BK	1-60w Med.	6¾"	7¾"	4½" W, 5¾" H Back Plate	

For posts and pier mounts, see pages 664-665.



1470 BK
13¾" W, 41" H



1440 BK
10½" W, 31" H



1449 BK
10½" W, 22¾" H



1410 BK
8¾" W, 25" H



1419 BK
8¾" W, 18" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE
1410 BK	3-25w Cand. or 1-60w Med.	10"	13¾"	4½" W, 6½" H
1419 BK	1-60w Med.	10"	13¾"	4½" W, 6½" H
1440 BK	3-25w Cand. or 1-75w Med.	13"	14½"	5" W, 8¼" H
1449 BK	3-25w Cand. or 1-75w Med.	13"	14½"	5" W, 8¼" H
1470 BK	3-40w Cand. or 1-100w Med.	14½"	19"	5" W, 8¼" H

CAMELOT™

FINISH BLACK
GLASS CLEAR BEVELED PANELS

Camelot's stunning clear beveled glass panels add a regal elegance to this traditional cast aluminum design in a rich Black finish.



1707 BK
12" W, 25½" H



1705 BK
12" W, 35" H



1700 BK
6½" W, 16" H



1704 BK
8½" W, 27" H



1702 BK
12" W, 25" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1700 BK	1-75w Med.	7½"	9¾"	4½" W, 7" H Back Plate	
1702 BK	3-40w Cand.			5" Dia. Canopy	6', 5'
1704 BK	3-40w Cand.	10"	17¼"	4½" W, 9" H Back Plate	
1705 BK	3-40w Cand.	14¼"	22½"	5¼" W, 14" H Back Plate	
1707 BK	3-40w Cand.			3" Dia. Post Fitter	

For posts and pier mounts, see pages 664-665.

Regal has a grand Old World style that features cast aluminum construction and elegant decorative stamped detailing in a Black Granite finish. Clear seedy water glass adds timeless sophistication.

FINISH BLACK GRANITE
GLASS CLEAR SEEDY WATER GLASS

REGAL™



1713 BG
11¾" W, 9¼" H



1726 BG
12" W, 32¼" H



1725 BG
8½" W, 23½" H



1722 BG
8½" W, 18½" H



1720 BG
6½" W, 13" H



1721 BG
8½" W, 22½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
1713 BG	4-40w Cand.				
1720 BG	2-40w Cand.	8¼"	4¾"	4¾" W, 9" H Back Plate	
1721 BG	3-40w Cand.				
1722 BG	3-40w Cand.			5" Dia. Canopy	6', 5'
1725 BG	3-40w Cand.	11¼"	7¼"	4¾" W, 14" H Back Plate	
1726 BG	4-40w Cand.	14¼"	10"	4¾" W, 18¼" H Back Plate	

For posts and pier mounts, see pages 664-665.

EDGEWATER™

FINISH BLACK
GLASS CLEAR SEEDY PANELS

Edgewater's classic design features durable cast aluminum and brass construction in a rich Black finish with clear seedy glass.

ADDITIONAL FINISHES
Oil Rubbed Bronze (OZ)



1675 BK
1675 BK-LL
15" W, 25½" H





1674 BK
6½" W, 11½" H

1676 BK
1676 BK-LL
10" W, 18" H

1683 BK
13" DIA., 6¾" H

1672 BK
1672 BK-LL
10" DIA., 19½" H

1670 BK
1670 BK-LL
10" W, 21" H

1671 BK
1671 BK-LL
10" DIA., 21¼" H

1677 BK
1677 BK-LL
15" DIA., 27¾" H
(shown as pier mount with 1304 BK)**

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
1670 BK	3-40w Cand.	1670 BK-LL	3-5w Cand. LED*	9½"	15¼"	5" W, 14" H Back Plate	
1671 BK	3-40w Cand.	1671 BK-LL	3-5w Cand. LED*			3" Dia. Post Fitter	
1672 BK	3-40w Cand.	1672 BK-LL	3-5w Cand. LED*			5" Dia. Canopy	6', 5'
1674 BK	1-60w Med.			6½"	4¾"	5" W, 7" H Back Plate	
1675 BK	4-40w Cand.	1675 BK-LL	4-5w Cand. LED*	13¾"	10½"	5" W, 14" H Back Plate	
1676 BK	3-40w Cand.	1676 BK-LL	3-5w Cand. LED*	9½"	7¼"	4¾" W, 9" H Back Plate	
1677 BK	4-40w Cand.	1677 BK-LL	4-5w Cand. LED*			3" Dia Post Fitter	
1683 BK	2-60w Med.						

*LED filament bulb included, see page 7. **Not for use within 4 ft. of ground. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

EDGEWATER™

FINISH OIL RUBBED BRONZE
GLASS CLEAR SEEDY PANELS

Edgewater's classic design features durable cast aluminum and brass construction in a rich Oil Rubbed Bronze finish with clear seedy glass.

ADDITIONAL FINISHES
Black (BK)



1675 OZ
1675 OZ-LL
15" W, 25½" H





1672 OZ
1672 OZ-LL
10" DIA., 19½" H

1674 OZ
6½" W, 11½" H

1676 OZ
1676 OZ-LL
10" W, 18" H

1683 OZ
13" DIA., 6¾" H

1670 OZ
1670 OZ-LL
10" W, 21" H

1671 OZ
1671 OZ-LL
10" DIA., 21¼" H

1677 OZ
1677 OZ-LL
15" DIA., 27¾" H

ITEM	MAXIMUM WATTAGE	LED ITEM	LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
1670 OZ	3-40w Cand.	1670 OZ-LL	3-5w Cand. LED*	9½"	15¼"	5" W, 14" H Back Plate	
1671 OZ	3-40w Cand.	1671 OZ-LL	3-5w Cand. LED*			3" Dia. Post Fitter	
1672 OZ	3-40w Cand.	1672 OZ-LL	3-5w Cand. LED*			5" Dia. Canopy	6', 5'
1674 OZ	1-60w Med.			6½"	4¾"	5" W, 7" H Back Plate	
1675 OZ	4-40w Cand.	1675 OZ-LL	4-5w Cand. LED*	13¾"	10½"	5" W, 14" H Back Plate	
1676 OZ	3-40w Cand.	1676 OZ-LL	3-5w Cand. LED*	9½"	7¼"	4¾" W, 9" H Back Plate	
1677 OZ	4-40w Cand.	1677 OZ-LL	4-5w Cand. LED*			3" Dia. Post Fitter	
1683 OZ	2-60w Med.						

*LED filament bulb included, see page 7. For complete product details and LED specifications, refer to hinkleylighting.com. For posts and pier mounts, see pages 664-665.

KEY WEST™

FINISH REGENCY BRONZE
GLASS CLEAR SEEDY

Key West captures a gracious elegance featuring cast aluminum construction and ornate decorative cast detailing in a Regency Bronze finish, complemented by clear seedy glass.



2905 RB
12" W, 27" H



2902 RB
12" DIA., 23¾" H



2904 RB
9" W, 21" H



2903 RB
15" DIA., 8¼" H



2900 RB
7" W, 16¼" H



2901 RB
12" DIA., 21¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2900 RB	1-60w Med.	9¼"	8¾"	4½" W, 7" H Back Plate	
2901 RB	3-60w Cand.			3" Dia. Post Fitter	
2902 RB	3-60w Cand.			5½" Dia. Canopy	6, 5'
2903 RB	2-60w Med.				
2904 RB	1-75w Med.	12¼"	12½"	4½" W, 9" H Back Plate	
2905 RB	3-60w Cand.	14¾"	13¾"	4½" W, 9" H Back Plate	

For posts and pier mounts, see pages 664-665.

SAN CLEMENTE™

FINISH COPPER BRONZE
GLASS CLEAR, BENT,
BEVELED AND BOUND

San Clemente's elegant shape takes center stage with clear bent, beveled and bound glass as the central design element. Cast aluminum and brass construction complemented by exquisite cast ornamental detailing completes its captivating appeal.

ADDITIONAL FINISHES
Museum Black (MB)



2446 CB
17" W, 25¾" H



2442 CB
14" DIA., 20" H

2443 CB
13¾" DIA., 9" H

2445 CB
14" W, 20¾" H

2440 CB
8½" W, 13¾" H

2444 CB
12¼" W, 19¾" H

2441 CB
14" DIA., 22¼" H
(shown as pier mount
with 1304 CB)*

2447 CB
17" DIA., 26¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/ CHAIN
2440 CB	1-60w Med.	9¼"	4¾"	4½" W, 7" H Back Plate	
2441 CB	3-40w Cand.			3" Dia. Post Fitter	
2442 CB	3-40w Cand.			5" Dia. Canopy	6, 5'
2443 CB	2-60w Med.			10¾" Dia. Canopy	
2444 CB	3-40w Cand.	12¼"	6¼"	4½" W, 9" H Back Plate	
2445 CB	3-40w Cand.	13¼"	6¼"	4½" W, 9" H Back Plate	
2446 CB	4-40w Cand.	15¾"	8¼"	5" W, 14" H Back Plate	
2447 CB	3-40w Cand.			3" Dia. Post Fitter	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

SAN CLEMENTE™

FINISH MUSEUM BLACK
GLASS CLEAR, BENT,
BEVELED AND BOUND

San Clemente's elegant shape takes center stage with clear bent, beveled and bound glass as the central design element. Cast aluminum and brass construction complemented by exquisite cast ornamental detailing completes its captivating appeal.

ADDITIONAL FINISHES
Copper Bronze (CB)



2446 MB
17" W, 25¾" H



2442 MB
14" DIA., 20" H



2444 MB
12 1/4" W, 19 3/4" H



2443 MB
13 3/4" DIA., 9" H



2440 MB
8 1/2" W, 13 3/4" H



2441 MB
14" DIA., 22 1/4" H



2447 MB
17" DIA., 26 1/4" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2440 MB	1-60w Med.	9 1/4"	4 3/4"	4 1/2" W, 7" H Back Plate	
2441 MB	3-40w Cand.			3" Dia. Post Fitter	
2442 MB	3-40w Cand.			5" Dia. Canopy	6, 5'
2443 MB	2-60w Med.			10 3/4" Dia. Canopy	
2444 MB	3-40w Cand.	12 1/4"	6 1/4"	4 1/2" W, 9" H Back Plate	
2446 MB	4-40w Cand.	15 3/4"	8 1/4"	5" W, 14" H Back Plate	
2447 MB	3-40w Cand.			3" Dia. Post Fitter	

For posts and pier mounts, see pages 664-665.

MONTICELLO™

FINISH COPPER BRONZE
GLASS CLEAR BENT,
BEVELED AND BOUND PANELS

Monticello's graceful curves emphasize its clear bent, beveled and bound glass panels. The durable solid brass construction showcases a rich Copper Bronze finish.



2336 CB
16" W, 26½" H



2332 CB
13" DIA., 20¼" H



2335 CB
13" W, 20½" H



2330 CB
9" W, 15¼" H



2334 CB
11¼" W, 19¼" H



2331 CB
13" DIA., 21¾" H
(shown as
pier mount with
1304 CB)*



2337 CB
16" DIA., 27" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2330 CB	1-60w Med.	9¾"	5"	4½" W, 7" H Back Plate	
2331 CB	3-40w Cand.			3" Dia. Post Fitter	
2332 CB	3-40w Cand.			5" Dia. Canopy	6', 5'
2334 CB	3-40w Cand.	12½"	6"	4½" W, 9¼" H Back Plate	
2335 CB	3-40w Cand.	13¼"	7"	5" W, 9¼" H Back Plate	
2336 CB	4-40w Cand.	15¾"	8"	4½" W, 16" H Back Plate	
2337 CB	4-40w Cand.			3" Dia. Post Fitter	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

AUGUSTA™

FINISH COPPER BRONZE
GLASS CLEAR BENT,
BEVELED AND BOUND PANELS

Augusta's sophisticated beauty showcases its stylish clear bent, beveled and bound glass. Constructed in solid brass with a Copper Bronze finish, this classic traditional design also offers removable scrolls.



2456 CB
15¾" W, 38¾" H



2452 CB
13¼" DIA., 27½" H



2454 CB
11¼" W, 27" H



2450 CB
8" W, 15½" H



2451 CB
13¼" DIA., 23¼" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/ CHAIN
2450 CB	1-60w Med.	8½"	7½"	4½" W, 6½" H Back Plate	
2451 CB	3-40w Cand.			3" Dia. Post Fitter	
2452 CB	3-40w Cand.			5" Dia. Canopy	6', 5'
2454 CB	3-40w Cand.	10½"	18¼"	4½" W, 15¾" H Back Plate	
2456 CB	4-40w Cand.	14½"	26¼"	5" W, 21¾" H Back Plate	

For posts and pier mounts, see pages 664-665.

CLIFTON PARK™

FINISH COPPER BRONZE
GLASS CLEAR, BEVELED
AND BOUND

Clifton Park has an aristocratic style that adds a dignified air to a home's façade. The sleek Copper Bronze finish, durable solid brass construction and clear beveled and bound glass add to the genteel style.



2429 CB
10¾" DIA., 6¾" H



2420 CB
6¾" W, 10¾" H



2428 CB
12¼" W, 25½" H



2426 CB
10½" W, 21½" H



2406 CB
17½" W, 36" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY
2406 CB	4-40w Cand.	15¼"	21¾"	4¾" W, 27¼" H Back Plate
2420 CB	1-60w Med.	6½"	4½"	4¾" W, 5½" H Back Plate
2426 CB	3-40w Cand.	10"	13¾"	4¾" W, 14¼" H Back Plate
2428 CB	3-40w Cand.	11½"	15¼"	4¾" W, 18¼" H Back Plate
2429 CB	2-60w Med.			8¾" Dia. Canopy



2422 CB
10½" DIA., 19¼" H



2424 CB
10½" W, 18½" H



2425 CB
9¼" W, 17¾" H



2423 CB
9¼" W, 14¾" H



2421 CB
12½" DIA., 23¾" H



2407 CB
17½" DIA., 26½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN
2407 CB	4-40w Cand.			3" Dia. Post Fitter	
2421 CB	3-40w Cand.			3" Dia. Post Fitter	
2422 CB	3-40w Cand.			5" Dia. Canopy	6', 5'
2423 CB	1-75w Med.	8¾"	6¼"	4¾" W, 7" H Back Plate	
2424 CB	3-40w Cand.	10"	7"	4¾" W, 7" H Back Plate	
2425 CB	2-40w Cand.	8¾"	11¼"	4¾" W, 12¾" H Back Plate	

For posts and pier mounts, see pages 664-665.

LUCERNE™

FINISH COPPER BRONZE
GLASS CLEAR BENT PANELS

Lucerne's grand silhouette features exquisite decorative cast detailing and solid brass construction in a Copper Bronze finish. Clear bent glass is captured in the fixture's gentle arches.



2315 CB
13¼" W, 30" H



2312 CB
13¼" DIA., 26½" H



2314 CB
10½" W, 24½" H



2310 CB
8½" W, 15" H



2317 CB
10½" DIA., 22¼" H
(shown as
pier mount with
1304 CB)*



2311 CB
13¼" DIA., 26½" H

ITEM	MAXIMUM WATTAGE	EXT.	TOP TO OUTLET	BACK PLATE/ CANOPY	WIRE/CHAIN
2310 CB	2-40w Cand.	10½"	4¾"	4¾" W, 7¼" H Back Plate	
2311 CB	4-40w Cand.			3" Dia. Post Fitter	
2312 CB	4-40w Cand.			5" Dia. Canopy	6', 5'
2314 CB	3-40w Cand.	13¾"	11½"	5" W, 16" H Back Plate	
2315 CB	4-40w Cand.	17¼"	13½"	5" W, 16" H Back Plate	
2317 CB	3-40w Cand.			3" Dia. Post Fitter	

*Not for use within 4 ft. of ground. For posts and pier mounts, see pages 664-665.

PIER MOUNTS



1301 BK



1304 BK



1304 BZ



1304 CB



1304 CW



1304 DZ



1304 HE



1304 KZ



1304 MB



1304 OB



1304 OZ



1304 RB



1304 SN



1305 OB



1307 BG



1307 MN



1307 MO



1307 MR



1307 PZ



1307 RK



1307 VK



1307 VZ



1308 AP



1308 MT

ITEM	FINISH	DIAMETER	BASE HEIGHT	FITTER DIAMETER
1301 BK	Black	3"	¼"	3"
1304 BK*	Black	7"	2"	3"
1304 BZ*	Bronze	7"	2"	3"
1304 CB*	Copper Bronze	7"	2"	3"
1304 CW*	Classic White	7"	2"	3"
1304 DZ*	Aged Zinc	7"	2"	3"
1304 HE*	Hematite	7"	2"	3"
1304 KZ*	Buckeye Bronze	7"	2"	3"
1304 MB*	Museum Black	7"	2"	3"
1304 OB*	Olde Bronze	7"	2"	3"
1304 OZ*	Oil Rubbed Bronze	7"	2"	3"
1304 RB*	Regency Bronze	7"	2"	3"
1304 SN*	Sienna	7"	2"	3"

ITEM	FINISH	DIAMETER	BASE HEIGHT	FITTER DIAMETER
1305 OB	Olde Bronze	7"	2"	3"
1307 BG	Black Granite	7"	2"	3"
1307 MN	Midnight Bronze	7"	2"	3"
1307 MO	Mocha	7"	2"	3"
1307 MR	Museum Bronze	7"	2"	3"
1307 PZ	Pearl Bronze	7"	2"	3"
1307 RK	River Rock	7"	2"	3"
1307 VK	Vintage Black	7"	2"	3"
1307 VZ	Victorian Bronze	7"	2"	3"
1308 AP	Antique Copper	7"	2"	3"
1308 MT	Metro Bronze	7"	2"	3"

Mounting hardware not included. *Concealed fasteners.

POSTS



ITEM	DIAMETER	HEIGHT	FITTER DIAMETER	WALL THICKNESS	CONSTRUCTION	ACCESSORIES INCLUDED/NOTES
6610 BK	3"	10'	3"	.072"	One-Piece Post, Aluminum	Ground Outlet, Photo Cell
6611 BK	3"	10'	3"	.072"	One-Piece Post, Aluminum	Photo Cell
6638 BK	3"	6½'	3"	.080"	Post, Cast Aluminum	Cast Aluminum Base
6660 BK	3"	7'	3"	.050"	One-Piece Post, Aluminum	
6660 BZ	3"	7'	3"	.050"	One-Piece Post, Aluminum	
6660 OI	3"	7'	3"	.050"	One-Piece Post, Aluminum	
6661 BK*	3"	7'	3"	.050"	One-Piece Post with Ladder Rest, Aluminum	
6662 BK	3"	7'	3"	.050"	One-Piece Post, Aluminum	Photo Cell
6663 BK*	3"	7'	3"	.050"	One-Piece Post with Ladder Rest, Aluminum	Photo Cell
6667 BK*	3"	7'	3"	.050"	One-Piece Post with Ladder Rest, Aluminum	Photo Cell and Ground Outlet
6680 BK	7¼"	18¼"	3"		Slip Base, Die Cast Aluminum	2-Piece, Used with Direct Burial Posts
6808 BK	10½"	8'	3"	.125"	Post, Cast Aluminum	Decorative Flange Bolt Cover

*Width including ladder rest is 16".

LUNA™ STEP

FINISH BRONZE, LIGHT
ALMOND, MATTE BRONZE,
SATIN WHITE, TITANIUM

The Luna step light is the perfect addition to any interior or exterior lighting plan and complements the Hinkley Luna outdoor lantern collection. A contemporary styled radius front die cast faceplate is included. The Luna step light is compatible with any decorator style faceplate and is easily retrofitted to any gang/receptacle location.



THE PERFECT SOLUTION FOR ANY INDOOR OR OUTDOOR 120V OUTLET OR SWITCH LOCATION

Single or Double Gang Configuration | Die-Cast Zinc Aluminum Alloy
4w Power Consumption | Dimmable




58506 LA
4½" W, 4½" H
 



58506 SW
4½" W, 4½" H
 

DOUBLE GANG CONFIGURATION



58506 TT
4½" W, 4½" H
 



58506 BZ
4½" W, 4½" H
 



58504 LA
3" W, 4½" H



58504 SW
3" W, 4½" H



58504 TT
3" W, 4½" H



58504 MZ
3" W, 4½" H



58504 BZ
3" W, 4½" H

SINGLE GANG CONFIGURATION

Compatible with any decorator style faceplate



58508 LA
4½" W, 3" H



58508 SW
4½" W, 3" H



58508 TT
4½" W, 3" H



58508 MZ
4½" W, 3" H



58508 BZ
4½" W, 3" H

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	EXT.
58504 BZ, LA, MZ, SW, TT	4w LED	240	2700K	90	20w	½"
58506 BZ, LA, SW, TT	4w LED	240	2700K	90	20w	½"
58508 BZ, LA, MZ, SW, TT	4w LED	240	2700K	90	20w	½"

For complete product details and LED specifications, refer to hinkleylighting.com.

NUVI™

FINISH BRONZE,
SANDSTONE, TITANIUM

NUVI offers exceptional 12v LED horizontal illumination due to its innovative composite optic technology. Constructed of durable, solid vinyl alloy NUVI is fit for harsh environments, offering resiliency and long-life. A diverse range of mounting opportunities and easy installation ensure maximum flexibility. ETL rated for indoor/outdoor use.



15444 BZ
3¼" L, 3" W, ¾" H



15444 ST
3¼" L, 3" W, ¾" H



15444 TT
3¼" L, 3" W, ¾" H



15446 BZ
5" L, 3" W, ¾" H



15446 ST
5" L, 3" W, ¾" H



15446 TT
5" L, 3" W, ¾" H



15448 BZ
10" L, 3" W, ¾" H




15448 TT
10" L, 3" W, ¾" H



15448 ST
10" L, 3" W, ¾" H

LED ITEM	INTEGRATED LED LIGHT SOURCE	LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY
15444 BZ, ST, TT	1.1w LED	60	2700K	80	7w
15446 BZ, ST, TT	1.9w LED	140	2700K	80	15w
15448 BZ, ST, TT	3.5w LED	260	2700K	80	25w

For complete product details and LED specifications, refer to hinkleylighting.com.



LANDSCAPE

EXPAND YOUR ENVIRONMENT WITH HINKLEY'S WIDE SELECTION OF LANDSCAPE LIGHTING




“Outdoor living is all about reconnecting with nature. Most of us have an innate desire to be outside, so when I design a space, the goal is to make that connection with nature seamless and comfortable. Lighting plays a huge part in setting the mood of the space.”

NICK MCCULLOUGH
MCCULLOUGH'S LANDSCAPE
AND NURSERY
COLUMBUS, OH

ABOVE: THE SHELTER COLLECTION | 1547KZ, HINKLEYLIGHTING.COM
OPPOSITE PAGE: THE TRELIS AND HARDY ISLAND COLLECTIONS
1435RB, PAGE 601 AND 16007MZ, HINKLEYLIGHTING.COM

WE'VE GOT YOU COVERED

CHECK OUT
HINKLEYLANDSCAPELIGHTING.COM
TO ILLUMINATE YOUR
OUTDOOR ENVIRONMENT



INDEX

1100		12304TT	455	1316MO	638	1429RB	602	1609MB	630	1664TT	464
1110DZ	438	12312BZ	454	1317MB	639	1430DZ	600	1609OZ	628	1665BZ	467
1110OZ	439	12312TT	454	1317MO	638	1430RB	603	1620KZ	528	1665SK	467
1112DZ	438	12314BZ	454	1319MB	639	1431DZ	599	1622KZ	528	1665TT	467
1112OZ	439	12314TT	454	1319MO	638	1431RB	602	1624KZ	528	1668BZ	463
1113DZ	438	1240MN	637	1320BK	488	1432DZ	600	1625KZ	528	1668SK	463
1113OZ	439	1241MN	637	1320HE	492	1432RB	603	1639BZ	476	1668TT	463
1114DZ	439	1242MN	637	1320KZ	490	1433DZ	599	1639SK	472	1669BZ	463
1114OZ	439	1243MN	637	1321BK	489	1433DZ-SCR	599	1639TT	474	1669SK	463
1120MR	519	1244MN	637	1321HE	493	1433RB	602	1640BZ	477	1669TT	462
1121MR	519	1245MN	636	1321KZ	491	1433RB-SCR	602	1640SK	473	1670BK	647
1122MR	519	1270OZ-WH	515	1322BK	489	1434DZ	600	1640SW	478	1670OZ	649
1124MR	519	1270VK	517	1322HE	493	1434RB	603	1640TT	475	1671BK	647
1125MR	519	1271OZ-WH	515	1322KZ	491	1435DZ	598	1641BZ	477	1671OZ	649
1126MR	519	1271VK	517	1324BK	488	1435RB	601	1641SK	473	1672BK	647
1129MR	518	1272OZ-WH	515	1324HE	492	1436DZ	600	1641TT	475	1672OZ	649
1140OL	617	1272VK	517	1324KZ	490	1436RB	603	1644BZ	477	1674BK	647
1140OL-CL	615	1273OZ-WH	515	1325BK	488	1437DZ	599	1644SK	473	1674OZ	649
1141OL	617	1273VK	517	1325HE	492	1437RB	602	1644SW	478	1675BK	646
1141OL-CL	615	1274OZ-WH	515	1325KZ	490	1438DZ	599	1644TT	475	1675OZ	648
1142OL	617	1274VK	517	1326BK	488	1438RB	602	1645BZ	477	1676BK	647
1143OL-CL	615	1275OZ-WH	514	1326HE	493	1439DZ	600	1645SK	473	1676OZ	649
1144OL	617	1275VK	516	1326KZ	491	1439RB	603	1645SW	478	1677BK	647
1144OL-CL	614			1328BK	489	1440BK	643	1645TT	475	1677OZ	649
1145OL	616	1300		1331MO	640	1441BK	642	1646BZ	477	1683BK	647
1147OL-CL	615	1301BK	664	1332MO	640	1445BK	642	1646SK	473	1683OZ	649
1148OL-CL	615	1304BK	664	1334MO	640	1449BK	643	1646SW	478		
1180SN	591	1304BZ	664	1335MO	640	1470BK	643	1646TT	475	1700	
1181SN	591	1304CB	664	1336MO	640	1471BK	642	1647BZ-LED	466	1700BK	644
1182SN	591	1304CW	664	1340BK	489	1490BK	525	1647SK-LED	466	1702BK	644
1184SN	591	1304DZ	664	1340HE	493	1491BK	525	1647SW-LED	466	1704BK	644
1185SN	590	1304HE	664	1340KZ	491	1492BK	525	1647TT-LED	466	1705BK	644
1187SN	591	1304KZ	664	1344BK	489	1494BK	525	1648BZ	477	1707BK	644
1192BK	436	1304MB	664	1344HE	493	1495BK	524	1648SK	473	1713BG	645
1192DZ	436	1304OB	664	1344KZ	491	1499BK	525	1648SW	478	1720BG	645
1192OZ	436	1304OZ	664	1390BK	520			1648TT	475	1721BG	645
1194BK	437	1304RB	664	1390BZ	521	1500		1649BZ	477	1722BG	645
1194DZ	437	1304SN	664	1391BK	520	15444BZ	668	1649SK	473	1725BG	645
1194OZ	437	1305OB	664	1391BZ	521	15444ST	668	1649SW	478	1726BG	645
		1307BG	664	1395BK	520	15444TT	668	1649TT	475	1741BK	534
1200		1307MN	664	1395BZ	521	15446BZ	668	1650BZ	477	1741HE	535
1200SN	589	1307MO	664	1396BK	520	15446ST	668	1650TT	475	1741OZ	536
1201SN	589	1307MR	664	1396BZ	521	15446TT	668	1655BZ	477	1742BK	534
1202SN	589	1307PZ	664	1397BK	520	15448BZ	668	1655TT	475	1742HE	535
1204SN	589	1307RK	664	1397BZ	521	15448ST	668	1659BZ	467	1742OZ	536
1205SN	589	1307VK	664			15448TT	668	1659SK	467	1744BK	534
1220BZ	451	1307VZ	664	1400				1659TT	467	1744HE	535
1220SK	452	1308AP	664	1410BK	643	1600		1660BZ	464	1744OZ	536
1220TT	450	1308MT	664	1412BK	642	1600MB	631	1660SK	464	1745BK	534
1224BZ	451	1311MB	639	1419BK	643	1600OZ	629	1660TT	464	1745HE	535
1224SK	452	1311MO	638	1420AI	618	1601MB	631	1661BZ	465	1745OZ	536
1224TT	450	1312MB	639	1421AI	618	1601OZ	629	1661SK	465	1750VZ	627
1225BZ	451	1312MO	638	1422AI	618	1602MB	631	1661TT	465	1751VZ	627
1225SK	452	1314MB	639	1424AI	618	1602OZ	629	1662BZ	465	1752VZ	627
1225TT	450	1314MO	638	1425AI	618	1604MB	631	1662SK	465	1754VZ	627
12302BZ	455	1315MB	639	1428DZ	600	1604OZ	629	1662TT	465	1765BZ	479
12302TT	455	1315MO	638	1428RB	603	1605MB	631	1664BZ	464	1765SK	479
12304BZ	455	1316MB	639	1429DZ	599	1605OZ	629	1664SK	464	1765SW	479

1765TT	479	1855DZ	579	1931RB	619	2100KZ	541	2231OZ	507	2350SK	456
1768BZ	479	1855LZ	581	1932RB	619	2101BK	543	2232OZ	507	2350SS	459
1768SK	479	1858DZ	578	1934RB	619	2101KZ	541	2234OZ	507	2350TT	457
1768SW	479	1858LZ	580	1935RB	619	2102BK	543	2235OZ	506	2354BZ	458
1768TT	479	1872BZ	469	1936RB	619	2102KZ	541	2237OZ	507	2354SK	456
1769BZ	479	1872TT	469	1950HE	553	2104BK	543	2240RB	527	2354SS	459
1769SK	479	1873BZ	468	1950VZ	552	2104KZ	541	2241RB	527	2354TT	457
1769SW	479	1873TT	468	1951HE	553	2105BK	542	2242RB	527	2355BZ	458
1769TT	479	1876BZ	469	1951VZ	552	2105KZ	540	2243RB	527	2355SK	456
1770SN	593	1876TT	469	1952HE	553	2106BK	543	2244RB	526	2355SS	459
1771SN	593	1877BZ	468	1952VZ	552	2106KZ	541	2246RB	527	2355TT	457
1772SN	593	1877TT	468	1954HE	553	2120PZ	621	2250BK	561	2360MB	605
1774SN	593	1880OZ	570	1954VZ	552	2121PZ	621	2251BK	561	2360OZ	607
1775SN	593	1882OZ	570	1956HE	553	2122PZ	621	2252BK	561	2361MB	605
		1884OZ	570	1956VZ	552	2123PZ	621	2254BK	561	2361OZ	607
		1890BK	633	1960MB	522	2124PZ	620	2255BK	561	2362MB	605
1800		1890RK	635	1960OZ	523	2126PZ	621	2258BK	560	2362OZ	607
1800BK	558	1891BK	633	1961MB	522	2128PZ	621	2271OZ	609	2364MB	605
1800CW	556	1891RK	635	1961OZ	523	2150KZ	533	2272OZ	609	2364OZ	607
1800OP	559	1892BK	633	1962MB	522	2154KZ	533	2274OZ	609	2365MB	605
1800OZ	557	1892RK	635	1962OZ	523	2155KZ	533	2275OZ	608	2365OZ	607
1801BK	558	1894BK	633	1964MB	522	2190BZ	483	2278OZ	609	2366MB	604
1801CW	556	1894RK	635	1964OZ	523	2190TT	481			2366OZ	606
1801OP	559	1895BK	633	1965MB	522	2191BZ	483	2300		2368MB	605
1801OZ	557	1895RK	635	1965OZ	523	2191TT	481	2300BK	485	2368OZ	607
1802BK	558	1895RK	635	1970BK	544	2192BZ	483		556	2370AS	588
1802CW	556	1898BK	633	1972BK	544	2192TT	481	2300KZ	487	2371AS	588
1802OP	559	1898RK	635	1974BK	544	2194BZ	483	2302BK	485	2372AS	588
1802OZ	557	1899BK	633			2194TT	481	2302KZ	487	2374AS	588
1804BK	558	1899RK	635	2000		2195BZ	483	2304BK	485	2376AS	588
1804CW	556			2010OZ	532	2195TT	481	2304KZ	487	2380OZ	550
1804OP	559	1900		2011OZ	532	2198BZ	482	2305BK	484	2382OZ	550
1804OZ	557	1900MT	499	2012OZ	532	2198TT	480	2305KZ	486	2384OZ	550
1805BK	558	1900SK	497	2015OZ	532			2306BK	485		
1805CW	556	1900SS	501	20300BZ	453	2200		2306KZ	487	2400	
1805OP	559	1901MT	499	20300TT	453	2200DZ	565	2307BK	485	2406CB	660
1805OZ	557	1901SK	497	20305BZ	453	2200SZ	567	2307KZ	487	2407CB	661
1807BK	558	1901SS	501	20305TT	453	2201DZ	565	2310CB	663	2410BZ	554
1807CW	556	1902MT	499	2040GS	585	2201SZ	567	2311CB	663	2410HE	555
1807OP	559	1902SK	497	2040SN	587	2202DZ	565	2312CB	663	2413BZ	554
1807OZ	557	1902SS	501	2041GS	585	2202SZ	567	2314CB	663	2413HE	555
1819BK	642	1904MT	499	2041SN	587	2203DZ	565	2315CB	662	2414BZ	554
18200AP	545	1904SK	497	2042GS	585	2203SZ	567	2317CB	663	2414HE	555
18204AP	545	1904SS	501	2042SN	587	2204DZ	565	2320OZ	505	2414HE	555
1830BZ	470	1905MT	499	2044GS	585	2204SZ	567	2321OZ	505	2420CB	660
1830SK	470	1905SK	497	2044SN	587	2205DZ	564	2322OZ	505	2421CB	661
1830TT	470	1905SS	501	2045GS	584	2205SZ	566	2324OZ	505	2422CB	661
1834BZ	470	1908MT	499	2045SN	586	2206DZ	565	2325OZ	504	2423CB	661
1834SK	470	1908SK	497	2047GS	585	2206SZ	567	2327OZ	505	2424CB	661
1834TT	470	1908SS	501	2047SN	587	2207DZ	565	2330CB	657	2425CB	661
1840BK	583	1909MT	498	2050KZ	471	2207SZ	567	2331CB	657	2426CB	660
1841BK	583	1909SK	496	2050TT	471	2220CB	623	2332CB	657	2428CB	660
1842BK	583	1909SS	500	2054KZ	471	2221CB	623	2334CB	657	2429CB	660
1844BK	583	1910OZ	529	2054TT	471	2222BB	289	2335CB	657	2440CB	653
1845BK	582	1911OZ	529	2090SB	563	2222CB	623	2336CB	656	2440MB	655
1850DZ	579	1912OZ	529	2091SB	563	2222PL	291	2337CB	657	2441CB	653
1850LZ	581	1914OZ	529	2092SB	563	2222PZ	286	2340OZ	568	2441MB	655
1851DZ	579	1915OZ	529	2094SB	563	2224CB	623	2341OZ	568	2442CB	653
1851LZ	581	1921BK	633	2095SB	563	2225CB	622	2342OZ	568	2442MB	655
1852DZ	579	1921RK	635			2226CB	623	2344OZ	568	2443CB	653
1852LZ	581	1929BK	632	2100		2227CB	623	2345OZ	568	2443MB	655
1854DZ	579	1929RK	634	2100BK	543	2230OZ	507	2350BZ	458	2444CB	653
1854LZ	581	1930RB	619								

2444MB	655	2600		2834BZ	447	29705WZ	440	3075AN	241	3138AN	099
2445CB	653	2611DZ	531	2834TT	447	29707VI	443	3075KZ	243	3138CM	099
2446CB	652	2611OZ	530	2835BZ	446	29707WZ	441	3076AN	241	3138OZ	099
2446MB	654	2612DZ	531	2835TT	446	2989SN	625	3076KZ	243	3139AN	098
2447CB	653	2612OZ	530	2850BZ	449	2990SN	625	3078AN	240	3139CM	098
2447MB	655	2614DZ	531	2850TT	449	2991SN	625	3078KZ	242	3139OZ	098
2450CB	659	2614OZ	530	2854BZ	449	2992SN	625	3097BN	080	3140AN	095
2451CB	659	2615DZ	531	2854TT	449	2995SN	625	3097DZ	080	3140CM	095
2452CB	659	2615OZ	530	2855BZ	448	2996SN	624	3097HB	080	3140OZ	095
2454CB	659	2618DZ	531	2855TT	448			3097OB	080	3143AN	095
2456CB	658	2618OZ	530	2860OZ	569	3000		3097PN	080	3143CM	095
2460OZ	595	2620DZ	548	2861OZ	569	3023DG	126			3143OZ	095
2461OZ	595	2624DZ	548	2862OZ	569	3023MM	127	3100		3144AN	095
2462OZ	595	2625DZ	548	2864OZ	569	3025DG	126	3110AN	099	3144CM	095
2464OZ	595	2630OB	613	2865OZ	569	3025MM	127	3110CM	099	3144OZ	095
2465OZ	594	2631OB	613	2890BK	495	3027DG	126	3110OZ	099	3146AN	095
2468OZ	595	2632OB	613	2890KZ	495	3027MM	127	3113AN	093	3146CM	095
2480BZ	554	2633OB	613	2894BK	495	3030BN	077	3113CM	093	3146OZ	095
2480HE	555	2634OB	613	2894KZ	495	3030DZ	074	3113OZ	093	3147AN	095
2484BZ	554	2635OB	613	2895BK	494	3030KZ	076	3114AN	094	3147CM	095
2484HE	555	2636OB	613	2895KZ	494	3030PN	075	3114CM	094	3147OZ	095
2490KZ	571	2639OB	612			3031BN	077	3114OZ	094	3148AN	094
2492KZ	571	2640OB	611	2900		3031DZ	074	3122DZ	083	3148CM	094
2494KZ	571	2641OB	611	2900RB	651	3031KZ	076	3122KZ	083	3148OZ	094
2495KZ	571	2642OB	611	2901RB	651	3031PN	075	3122PL	083	3149AN	095
2497KZ	571	2643OB	611	2902RB	651	3033BN	077	3122PN	083	3149CM	095
		2644OB	611	2903RB	651	3033DZ	074	3122PT	081	3149OZ	095
2500		2645OB	611	2904RB	651	3033KZ	076	3123CM	085	3150AN	095
2500BK	641	2646OB	611	2905RB	650	3033PN	075	3123KZ	085	3150CM	095
2501BK	641	2649OB	610	2910DZ	547	3034BN	077	3123PL	085	3150OZ	095
2502BK	641			2910OZ	546	3034DZ	074	3124CM	084	3151AN	095
2504BK	641	2700		2911DZ	547	3034KZ	076	3124KZ	084	3151CM	095
2505BK	641	2714BZ	460	2911OZ	546	3034PN	075	3124PL	084	3151OZ	095
2560OZ	597	2714SS	460	2914DZ	547	3040AN	102	3126DZ	082	3162AN	304
2561OZ	597	2715BZ	460	2914OZ	546	3040CM	102	3126KZ	082	3162BR	304
2562OZ	597	2715SS	460	2915DZ	547	3040OZ	102	3126PL	082	3162OZ	304
2564OZ	597	2722DZ	549	2915OZ	546	3041AN	101	3126PN	082	3170AN	092
2565OZ	596	2722KZ	549	29201SQ	435	3041CM	101	3126PT	081	3170CM	092
2570AR	513	2740OZ	537	29202SQ	435	3041OZ	101	3127CM	084	3170OZ	092
2570SK	511	2742OZ	537	29203SQ	435	3043AN	102	3127KZ	084	31700AN	091
2570TT	509	2744OZ	537	29205SQ	435	3043CM	102	3127PL	084		375
2571AR	513	2745OZ	537	29206SQ	435	3043OZ	102	3128AN	098	31700CM	091
2571SK	511	2790OZ	538	29208SQ	434	3044AN	101	3128CM	098		375
2571TT	509	2790OZ-CL	539	2920BZ	503	3044CM	101	3128OZ	098	31700OZ	091
2572AR	513	2791OZ	538	2920PS	502	3044OZ	101	3129AN	098		375
2572SK	511	2791OZ-CL	539	2922BZ	503	3045AN	102	3129CM	098	3171AN	092
2572TT	509	2792OZ	538	2922PS	502	3045CM	102	3129OZ	098	3171CM	092
2573AR	513	2792OZ-CL	539	2924BZ	503	3045OZ	102	3130AN	097	3171OZ	092
2573SK	511	2794OZ	538	2924PS	502	3046AN	101	3130CM	097	3173AN	092
2573TT	509	2794OZ-CL	539	2925BZ	503	3046CM	101	3130OZ	097		374
2574AR	513	2795OZ	538	2925PS	502	3046OZ	101	3133AN	097	3173CM	092
2574SK	511	2795OZ-CL	539	2930DZ	577	3047AN	101	3133CM	097		374
2574TT	509			2931DZ	577	3047CM	101	3133OZ	097	3173OZ	092
2575AR	513	2800		2932DZ	577	3047OZ	101	3134AN	097		374
2575SK	511	2800DZ	573	2934DZ	577	3048AN	103	3134CM	097	3174AN	092
2575TT	509	2801DZ	573	2935DZ	576	3048CM	103	3134OZ	097	3174CM	092
2576AR	513	2802DZ	573	29616IR	433	3048OZ	103	3136AN	098	3174OZ	092
2576SK	511	2804DZ	573	29700VI	443	3054AN	078	3136CM	098	3175AN	092
2576TT	509	2805DZ	572	29700WZ	441	3054GS	078	3136OZ	098	3175CM	092
2579AR	512	2806DZ	573	29703VI	443	3054RB	078	3137AN	098	3175OZ	092
2579SK	510	2830BZ	447	29703WZ	441	3072AN	241	3137CM	098	3176AN	092
2579TT	508	2830TT	447	29705VI	442	3072KZ	243	3137OZ	098	3176CM	092

3176OZ	092	3220OB-WH	187	3302AN-CL	306	3397RS	061	3497AN	113	3616PW	298
3177AN	092	3221AN	191	3302BR	306	3397GV	062	3497OZ	113	3641BN	315
3177CM	092	3221OB	189	3302BR-CL	306	3397PL	063			3641CM	315
3177OZ	092	3221OB-WH	187	3302CM	306			3500		3641HB	315
3178AN	093	3222AN	191	3302CM-CL	306	3400		3502OL	270	3641OZ	315
	377	3222OB	189	3302OZ	306	3407BN	123	3503OL	269	3643BN	314
3178CM	093	3222OB-WH	187	3302OZ-CL	306	3407HB	123	3504OL	270	3643CM	314
	377	3223AN	191	3304AN	307	3407KZ	123	3506OL	270	3643HB	314
3178OZ	093	3223OB	189	3304BR	307	3413BZ	237	3508OL	271	3643OZ	314
	377	3223OB-WH	187	3304CM	307	3413DZ	236	3512OR	146	3650AN	303
3198AN	100	3224AN	190	3304OZ	307	3414BZ	237	3512PN	147	3650HB	303
3198CM	100	3224OB	188	3308AN	309	3414DZ	236	3514OR	146	3650OZ	303
3198OZ	100	3224OB-WH	186	3308AN-QF	309	3415BZ	237	3514PN	147	3650PN	303
		3225AN	191	3308BR	309	3415DZ	236	3515OR	146	3684BN	112
		3225OB	189	3308BR-QF	309	3418BZ	237	3515PN	147	3684CM	112
		3225OB-WH	187	3308CM	309	3418DZ	236	3521AN	183	3684OZ	112
3200AN	169	3226AN	191	3308CM-QF	309	3440PN	156	3521BC	182	3685BN	033
3200BR	173	3226OB	189	3308OZ	309	3440VS	157	3521CM	184	3685CM	033
3200KZ	177	3226OB-WH	187	3308OZ-QF	309	3441PN	156	3522AN	183	3685OZ	033
3201AN	169	3228AN	191	3330BZ	138	3441VS	157	3522BC	182	3686BN	033
3201BR	173	3228AN-QF	191	3330DZ	134	3444PN	156	3522CM	184	3686CM	033
3201KZ	177	3228OB	189	3332BZ	139	3444VS	157	3523AN	183	3686OZ	033
3202AN	170	3228OB-QF	189	3332DZ	135	3447PN	156	3523BC	182	3687BN	112
3202BR	174	3228OB-WH	187	3334BZ	138	3447VS	157	3523CM	184	3687CM	112
3202KZ	178	3228OB-WH-QF	187	3334DZ	134	3460CG	149	3560BV	161	3687OZ	112
3203AN	169	3231BN	311	3335BZ	139	3460SB	151	3563BV	161	3688BN	033
3203BR	173	3231DZ	311	3335DZ	135	3463CG	149	3564BV	161	3688CM	033
3203KZ	177	3231OZ	311	3336BZ	137	3463SB	151	3566BV	160	3688OZ	033
3204AN	169	3233BN	311	3336DZ	133	3464CG	148	3567BV	161	3689BN	033
3204BR	173			3337BZ	138	3464SB	150	3574DZ	125	3689CM	033
3204KZ	177			3337DZ	134	3466CG	149	3576DZ	125	3689OZ	033
3205AN	171			3338BZ	138	3466SB	151	3580PN	155		
3205BR	175	3233DZ	311	3338DZ	134	3468CG	149	3580VS	153	3700	
3205KZ	179	3233OZ	311	3351BZ	137	3468SB	151	3582PN	155	3700KZ	181
3206AN	168	3254BN	073	3351DZ	133	3469CG	149	3582VS	153	3701KZ	181
3206BR	172	3254CM	073	3355BZ	139	3469SB	151	3585PN	155	3703KZ	181
3206KZ	176	3254OZ	073	3355DZ	135	3470HR	261	3585VS	153	3704KZ	181
3207AN	170	3257BN	073	3357BZ	137	3470OB	263	3586PN	155	3705KZ	180
3207BR	174	3257CM	073	3357DZ	133	3470PN	257	3586VS	153	3712FB	301
3207KZ	178	3257OZ	073	3358BZ	136	3470PW	259	3587PN	155	3713FB	301
3208AN	171	3260IN	057	3358DZ	132	3472HR	261	3587VS	153	3714FB	301
3208BR	175	3263IN	057	3380AN	115	3472OB	263	3588PN	154	3716FB	301
3208KZ	179	3265IN	057	3380HB	119	3472PN	257	3588VS	152	3773GZ	067
3209AN	170	3266IN	056	3380LZ	117	3472PW	259	3592OZ	245	3773PN	065
3209BR	174	3267IN	057	3381AN	115	3473HR	261	3595OZ	245	3774GZ	066
3209KZ	178	3274BZ	124	3381HB	119	3473OB	263	3598OZ	245	3774PN	064
3210AN	170	3275BZ	124	3381LZ	117	3473PN	257	3599OZ	244	3776GZ	067
3210BR	174	3277BZ	124	3382AN	115	3473PW	259			3776PN	065
3210KZ	178			3382HB	119	3474HR	261	3600		3777GZ	067
3211AN	169	3300		3382LZ	117	3474OB	263	3604GV	079	3777PN	065
3211BR	173	3300AN	308	3384AN	115	3474PN	257	3604KZ	079	3782AN	402
3211KZ	177	3300AN-CL	308	3384HB	119	3474PW	259	3610BB	297	3782HB	310
3212AN	171	3300BR	308	3384LZ	117	3478HR	261	3610OB	299	3782OZ	310
3212BR	175	3300BR-CL	308	3385AN	114	3478OB	263	3610PW	298	3783AN	310
3212KZ	179	3300CM	308	3385HB	118	3478PN	257	3612BB	297	3783HB	310
3214AN	170	3300CM-CL	308	3385LZ	116	3478PW	259	3612OB	299	3783OZ	310
3214BR	174	3300OZ	308	3394RS	061	3479HR	260	3612PW	298	3793BN	165
3214KZ	178	3300OZ-CL	308	3394GV	062	3479OB	262	3613BB	297	3793KZ	167
3217AN	171	3301AN	309	3394PL	063	3479PN	256	3613OB	299	3794BN	165
3217BR	175	3301BR	309	3395RS	060	3479PW	258	3613PW	298	3794KZ	167
3217KZ	179	3301CM	309	3395GV	062	3494AN	113	3616BB	297	3796BN	164
3220AN	191	3301OZ	309	3395PL	063	3494OZ	113	3616OB	299	3796KZ	166
3220OB	189	3302AN	306								

3797BN	165	4019OL-CL	266	4323OZ	253	4535OZ	143	4653OB	213	4669OB-CL	207
3797KZ	167	4020AN	225	4323PN	253	4538DZ	140	4653OB-CL	205	4669OB-OPAL	211
3800		4021AN	225	4325HB	252	4538OZ	142	4653OB-OPAL	209	4671BN	218
3843OZ	120	4023AN	225	4325OZ	253	4570KZ	201	4655BN	217	4671OB	214
3844OZ	120	4024AN	225	4325PN	253	4571KZ	201	4655BR	203	4671OB-CL	206
3870BN	195	4025AN	225	4353LZ	254	4572KZ	201	4655OB	213	4671OB-OPAL	210
3871BN	195	4027AN	225	4353PL	255	4574KZ	201	4655OB-CL	205		
	365	4028AN	224	4354LZ	254	4575KZ	201	4655OB-OPAL	209	4700	
3871CM	364	4090RI	264	4354PL	255	4576KZ	200	4656BN	217	4700SH	293
3872BN	195	4094RI	264	4358LZ	254	4577KZ	201	4656BR	203	4744BN	122
3873BN	194	4099RI	264	4358PL	255	4600		4656OB	213	4744OZ	122
3874BN	195	4100		4360DZ	108	4600OZ	235	4656OB-CL	205	4750BC	158
3875BN	194	4102BB	289	4360PN	107	4600SH	234	4656OB-OPAL	209	4750PN	159
3876BN	194		425	4363DZ	108		235	4657BN	217	4750SH	158
3877BN	195	4102CB	623	4363KZ	109	4600WT	234	4657BR	202		159
3878BN	193	4102PL	291	4363PN	107	4604OZ	235	4657OB	213	4752BC	158
			424	4364DZ	108	4604WT	234	4657OB-CL	205	4752PN	159
3900		4102PZ	286	4364KZ	109	4605OZ	235	4657OB-OPAL	209	4752SH	158
3910IR	059	4103BB	289	4364PN	107	4605WT	234	4659BN	216		159
3910SH	059	4103PL	291	4367DZ	108	4620FB	301	4659OB	212	4753BC	158
3913IR	059	4103PZ	286	4367KZ	109	4622FB	301	4659OB-CL	204	4753PN	159
3916IR	059	4140BB	289	4367PN	107	4626FB	300	4659OB-OPAL	208	4756BC	158
3918IR	058	4140PZ	286	4381BN	313	4630BN	221	4660BN	219	4756PN	159
3920KZ	144	4200		4381KZ	313		414	4660OB	215	4771SL	293
3920PL	145	4240OB	282	4382BN	313	4630OB	415	4660OB	390	4772SL	293
3924KZ	144	4240PL	279	4382KZ	313	4630OZ-WH	223	4660OB-CL	207	4774SL	293
3924PL	145	4243OB	282	4400		4631BN	221		389	4775SL	293
3925KZ	144	4243PL	279	4400GR	295		414	4660OB-OPAL	211	4776SL	293
3925PL	145	4245OB	282	4401OW	295	4631OZ-WH	223		388	4778SL	293
3927KZ	144	4245PL	279	4404GR	295	4632BN	221	4661BN	217	4779SL	292
3927PL	145	4246OB	282	4405GR	295	4632OZ-WH	223	4661OB	213	4780OZ	069
3971BN	312	4246PL	279	4408GR	294	4636BN	221	4661OB-CL	205	4780PL	071
3971KZ	312	4247OB	283	4410BB	296	4636OZ-WH	223	4661OB-OPAL	209	4783OZ	069
3972BN	312	4247PL	280	4410OB	299	4637BN	221	4662BN	218	4783PL	071
3972KZ	312	4248OB	282	4410PW	298	4637OZ-WH	223	4662OB	214	4784OZ	071
3992BN	198	4248PL	279	4412BB	296	4638BN	221	4662OB-CL	206	4784PL	071
3992OZ	199	4249OB	281	4412OB	299	4638OZ-WH	223	4662OB-OPAL	210	4786OZ	069
3996BN	198	4249PL	278	4412PW	298	4639BN	220	4663BN	218	4786PL	071
3996OZ	199	4254OB	283	4415BB	297	4639OZ-WH	222	4663OB	214	4788OZ	069
3997BN	198	4254PL	280	4416BB	297	4640BB	297	4663OB-CL	206	4788PL	071
3997OZ	199	4258OB	283	4417BB	296	4642BB	297	4663OB-OPAL	210	4789OZ	068
4000		4258PL	280	4419BB	296	4650BN	218	4664BN	219	4789PL	070
4000SH	233	4259OB	283	4421OW	296		386	4664OB	215	4790BN	273
4002PN	233	4259PL	280		299	4650BN-CL	387	4664OB-CL	207	4790EZ	276
4005PN	233	4273WZ	053	4483EN	163	4650BR	203	4664OB-OPAL	211	4791BN	274
4006PN	232	4274WZ	053	4484EN	163	4650OB	214	4665BN	219	4791EZ	277
4010OL	271	4275WZ	053	4485EN	162		390	4665OB	215	4792BN	273
	423	4276WZ	053	4492PL	239	4650OB-CL	206	4665OB-CL	215	4792EZ	276
4010OL-CL	267	4278WZ	053	4493PL	239	4650OB-OPAL	210	4665OB-CL	207	4793BN	274
	422	4279WZ	052	4494PL	239	4651BN	219	4665OB-OPAL	211	4793EZ	277
4013OL	269	4300		4497PL	239	4651BR	203	4666BN	218	4794BN	274
4013OL-CL	267	4300OL	269	4500		4651OB	215	4666OB	214	4794EZ	277
4015OL	269	4300OL-CL	267	4522AI	265	4651OB-CL	207	4666OB-CL	206	4795BN	274
4015OL-CL	267		422	4526AI	265	4651OB-OPAL	211	4666OB-OPAL	210	4795EZ	277
4016OL	270	4304OL	271	4528AI	265	4651OB-OPAL	211	4667BN	217	4796BN	273
4017OL	271	4308OL	270	4530DZ	141	4652BN	219	4667BR	203	4796EZ	276
4017OL-CL	267	4309OL	268	4534DZ	141	4652BR	203	4667OB	213	4797BN	274
4018OL	269	4314OL	271	4534OZ	143	4652OB	215	4667OB-CL	205	4797EZ	277
4018OL-CL	267	4323HB	253	4535DZ	141	4652OB-CL	215	4667OB-OPAL	209	4798BN	273
4019OL	269					4652OB-OPAL	211	4669BN	219	4798EZ	276
						4653BN	217	4669BR	203	4799BN	272
						4653BR	203	4669OB	215	4799EZ	275

4800

4811DZ	131
4811KZ	129
4813DZ	131
4813KZ	129
4814DZ	131
4814KZ	129
4815DZ	130
4815KZ	128
4818DZ	131
4818KZ	129
4820IR	055
4823IR	055
4824IR	055
4825IR	055
4826IR	054
4834DZ	087
4834DZ-PN	087
4834PN	087
4835DZ	087
4835DZ-PN	087
4836DZ	086
4836DZ-PN	086
4870AN	231
4870BR	229
4872AN	231
4872BR	229
4875AN	231
4875BR	229
4876AN	231
4876BR	229
4878AN	230
4878BR	228
4880BB	288
4880PL	291
4880PZ	285
4881BB	289
	425
4881CB	623
4881PL	291
	424
4881PZ	286
4885BB	289
4885PL	291
4885PZ	286
4886BB	288
4886PL	290
4886PZ	285
4887BB	288
4887PZ	285
4889BB	287
4889PZ	284
4900	
4900BN	273
4900EZ	276
4911SL	227
4912SL	227
4913SL	227
4914SL	227
4915SL	226

4916SL	227
4933HB	104
4933PL	105
4935HB	104
4935PL	105
4937HB	104
4937PL	105
4943TZ	072
4946TZ	072
4952HB	249
4952LZ	251
4952PL	247
4956HB	249
4956LZ	251
4956PL	247
4958HB	249
4958LZ	251
4958PL	247
4959HB	248
4959LZ	250
4959PL	246
4970BN	197
4971BN	197
4972BN	197
4975BN	197
4978BN	196
5000	
5000AN	418
5000OB	417
5000SL	416
5002AN	418
5002OB	417
5002SL	416
5003AN	418
5003OB	417
5003SL	416
5004AN	418
5004OB	417
5004SL	416
5005AN	418
5005OB	417
5005SL	416
50020AN	376
50020CM	376
50020OZ	376
50021AN	376
50021CM	376
50021OZ	376
50023AN	376
50023CM	376
50023OZ	376
50024AN	376
50024CM	376
50024OZ	376
50025AN	374
50025CM	374
50025OZ	374
50026AN	376
50026CM	376
50026OZ	376

50027AN	374
50027CM	374
50027OZ	374
50028AN	377
50028CM	377
50028OZ	377
5002OB	417
50030AN	376
50030CM	376
50030OZ	376
50031AN	376
50031CM	376
50031OZ	376
50033AN	376
50033CM	376
50033OZ	376
50034AN	376
50034CM	376
50034OZ	376
50035AN	376
50035CM	376
50035OZ	376
50036AN	374
50036CM	374
50036OZ	374
50037AN	376
50037CM	376
50037OZ	376
50038AN	377
50038CM	377
50038OZ	377
5003AN	418
5003OB	417
5004AN	418
5004OB	417
5010BN	410
5010CM	411
5012BN	410
5012CM	411
5013BN	410
5013CM	411
5014BN	410
5014CM	411
50122AN	375
50122AN	375
50122OZ	375
50123AN	375
50123CM	375
50123OZ	375
5020BN	346
5020CM	347
5020KZ	348
5022BN	346
5022CM	347
5022KZ	348
5023BN	346
5023CM	347
5023KZ	348
5024BN	346
5024CM	347
5024KZ	348

5025BN	346
5025CM	347
5025KZ	348
5050BN	355
5050CM	354
5052BN	355
5052CM	354
5053BN	355
5053CM	354
5054BN	355
5054CM	354
5100	
5100AN	343
5100BR	345
5100KZ	344
5102AN	343
5102BR	345
5102KZ	344
5103AN	343
5103BR	345
5103KZ	344
5104AN	343
5104BR	345
5104KZ	344
5105AN	343
5105BR	345
5105KZ	344
51100CM	342
51102CM	342
51103CM	342
51104CM	342
5120PB	021
5122BK	298
5124PB	021
51800BN-CL	401
51800PN	400
51802BN-CL	401
51802PN	400
51803BN-CL	401
51803PN	400
51804BN-CL	401
51804PN	400
51812BN	325
51812PN	325
51814BN	325
51814PN	325
51820BN	372
51820KZ	371
51820PN	370
51822BN	372
51822KZ	371
51822PN	370
51823BN	372
51823KZ	371
51823PN	370
51824BN	372
51824KZ	371
51824PN	370
51825BN	372
51825KZ	371

51825PN	370
5190CM	384
5191CM	384
5192CM	384
5193CM	384
5194CM	384
5200	
52112BN	323
52112PN	323
52230BN	396
52232BN	396
52233BN	396
52234BN	396
5232BN	328
5232CM	329
5234BN	328
5234CM	329
5236BN	328
5236CM	329
52400BN	338
52402BN	338
52403BN	338
5250AN	362
5250CM	363
5252AN	362
5252CM	363
5253AN	362
5253CM	363
5254AN	362
5254CM	363
5255AN	362
5255CM	363
5260OZ	143
5260PN	369
5262OZ	368
5262PN	369
5263OZ	368
5263PN	369
5280AN	412
5280PN	413
5282AN	412
5282PN	413
5283AN	412
5283PN	413
5284AN	412
5284PN	413
5290AN	378
5290PN	379
5292AN	378
5292PN	379
5293AN	378
5293PN	379
5300	
53010BC	399
53010BN	397
53010PN	398
53012BC	399
53012BN	397


53012PN	398
53013BC	399
53013BN	397
53013PN	398
53014BC	399
53014BN	397
53014PN	398
5310BB	289
	425
5310PL	291
	424
5310PZ	286
5312BB	425
5312PL	424
5313BB	425
5313PL	424
5314BB	425
5314PL	424
5317BB	288
5317PL	291
5317PZ	285
5350PL	366
5350PN	367
5352PL	366
5352PN	367
5353PL	366
5353PN	367
5354PL	366
5354PN	367
5357PL	366
5357PN	367
53550BN	331
53550CM	330
53552BN	331
53552CM	330
53553BN	331
53553CM	330
53554BN	331
53554CM	330
5362BN	414
5362OB	415
5363BN	414
5363OB	415
5370BN	385
5372BN	385
5373BN	385
5375BN	385
53842BN	322
53842PN	322
53844BN	322
53844PN	322
5400	
5421BN	328
5421CM	329
5421BR	345
5440BN	373
5442BN	373
5443BN	373
5444BN	373
5444BN	373
54620BN	359

54620CM	358	55654BN	324	5656BN	340	5853BC	405	59923CM	321	83667BN	033
54622BN	359	55654PN	324	5656CM	339	5853BN	406	59924BN	320	83667CM	033
54622CM	358	5580BB	421	5656OZ	341	5853CM	407	59924CM	321	83667OZ	033
54623BN	359	5580PL	420	56670AN	394	5854BC	405			83669AN	033
54623CM	358	5582BB	421	56670PN	395	5854BN	406	6100		83669BN	033
54624BN	359	5582PL	420	56672AN	394	5854CM	407	61033BN	305	83669CM	033
54624CM	358	5583BB	421	56672PN	395	5855BC	405	61033OZ	305	83669OZ	033
54812BN	326	5583PL	420	56673AN	394	5855BN	406	61111BN	305		
54812CM	326	5584BB	421	56673PN	395	5855CM	407	61111OZ	305	FR4900	
54814BN	326	5584PL	420	56674AN	394	58780BN	402	61222BN	305	FR49190SLF	426
54814CM	326	5585BB	421	56674PN	395	58780CM	403	61222OZ	305		
		5585PL	420			58780OZ	404			FR5900	
5500		5590BN	195	5700		58782BN	402	6300		FR59192SLF	426
55020BN	357		365	57130CM	353	58782CM	403	63306BK-CL	111	FR59193SLF	426
55020PN	356	5590CM	364	57132CM	353	58782OZ	404	63306BK-SM	110	FR59194SLF	426
55022BN	357	5592BN	365	57133CM	353	58783BN	402	63307BK-CL	111		
55022PN	356	5592CM	364	57134CM	353	58783CM	403	63307BK-SM	111		
55023BN	357	5593BN	365	5740AN	408	58783OZ	404	63307BN-CL	111		
55023PN	356	5593CM	364	5740BR	409	58784BN	402	63307BN-SM	111		
55024BN	357	5594BN	365	5742AN	408	58784CM	403	63307CM-MR	111		
55024PN	356	5594CM	364	5742BR	409	58784OZ	404	63307CM-SM	111		
5542OL	423			5743AN	408	5892BN	386				
5542OL-CL	422	5600		5743BR	409	5892BN-CL	387	6600			
5543OL	423	5600CM	383	5744AN	408	5892OB	390	6610BK	665		
5543OL-CL	422	56010CM	333	5744BR	409	5892OB-CL	389	6611BK	665		
5544OL	423	56012CM	333	57550BN	360	5892OB-OPAL	388	6638BK	665		
5544OL-CL	422	56013CM	333	57550PN	361	5893BN	386	6660BK	665		
5545OL	423	56014CM	333	57552BN	360	5893BN-CL	387	6660BZ	665		
5545OL-CL	422	5602CM	383	57552PN	361	5893OB	390	6660OI	665		
55482CM	332	5603CM	383	57553BN	360	5893OB-CL	389	6661BK	665		
55483CM	332	5604CM	383	57553PN	361	5893OB-OPAL	388	6662BK	665		
55484CM	332	56320AN	419	57554BN	360	5894BN	386	6663BK	665		
5550BN	352	56322AN	419	57554PN	361	5894BN-CL	387	6667BK	665		
5550CM	351	56323AN	419			5894OB	390	6680BK	665		
5550CM-CL	350	5650BN	340	5800		5894OB-CL	389	6808BK	665		
5550KZ	349	5650CM	339	5830AN	393	5894OB-OPAL	388				
5551BR	392	5650OZ	341	5830BR	392	5895BN	386	6700			
5551BN	393	5651BN	198	5832AN	393	5895BN-CL	387	67001EN	090		
5551CM	382		340	5832BR	392	5895OB	390	67001OZ	090		
5552BN	352	5651CM	339	5833AN	393	5895OB-CL	389	67002EN	090		
5552CM	351	5651OZ	341	5833BR	392	5895OB-OPAL	388	67002OZ	090		
5552CM-CL	350	5651OZ	199	5834AN	393			67003EN	090		
5552KZ	349		341	5834BR	392	5900		67003OZ	090		
5553BN	352	5652BN	340	5850BC	405	5920BN	336	67011EN	089		
5553CM	351	5652CM	339	5850BN	406	5920BR	337	67011OZ	089		
5553CM-CL	350	5652OZ	341	5850CM	407	5920CM	335	67012EN	089		
5553KZ	349	5654BN	340	58504BZ	667	5922BN	336	67012OZ	089		
5554BN	352	5654CM	339	58504LA	667	5922BR	337	67013EN	089		
5554CM	351	5654OZ	341	58504SW	667	5922CM	335	67013OZ	089		
5554CM-CL	350	56550BN	381	58504TT	667	5923BN	336	67071EN	088		
5554KZ	349	56550KZ	380	58506BZ	666	5923BR	337	67071OZ	088		
5555BN	352	56550PN	382	58506LA	666	5923CM	335	67072EN	088		
5555CM	351	56552BN	381	58506SW	666	5924BN	336	67072OZ	088		
5555CM-CL	350	56552KZ	380	58506TT	666	5924BR	337	67073EN	088		
5555KZ	349	56552PN	382	58508BZ	667	5924CM	335	67073OZ	088		
5556BN	352	56553BN	381	58508LA	667	5925BN	336				
5556CM	351	56553KZ	380	58508SW	667	5925BR	337	8000			
5556CM-CL	350	56553PN	382	58508TT	667	5925CM	335	80100QF	185		
5556KZ	349	56554BN	381	5852BC	405	5925BN	336				
55652BN	324	56554KZ	380	5852BN	406	59922CM	321	8300			
55652PN	324	56554PN	382	5852CM	407	59923BN	320	83667AN	033		



"The unexpected always trumps the predictable and safe. It exudes confidence and personality and is what makes each of us and our homes unique."

ABOVE: THE FENMORE + TRELLIS COLLECTIONS | 4946TZ, PAGE 72 AND 1436RB, PAGE 600



JILL SHARP WEEKS
JILL SHARP STUDIO
CHARLESTON, SC

We want you to enjoy your experience with Hinkley.

There is nothing complicated about it: we want to deliver a great product and treat you the way we'd like to be treated. So whether you are flipping through our catalog, surfing our site, getting inspired through social media, chatting with a member of our team or checking out our lighting in a retail shop—we want it to be time well-spent. Here's all you need to know:

CATALOG COLLECTIONS

Hinkley catalogs feature our current and complete product line along with important product specs and detailed photography. A must for the print-loving researcher who likes to tab their favorites. Stop by your local showroom for your own copy.

HINKLEYLIGHTING.COM

Dive in! Our easy-to-use site makes your product research process a snap, with the added benefit of tips, trends, installation guidelines and a quick connection to our retail partners.

SOCIAL CLIMBERS

We don't mean to brag, but we are connected. Look for @hinkleylighting on:



REAL PEOPLE

Want to chat? Contact us at service@hinkleylighting.com or 1.800.HINKLEY.

Hinkley Lighting stands behind the quality of our lighting fixtures with product warranties that are among the strongest in the industry. For details of warranty coverage on specific products, please refer to hinkleylighting.com or consult a qualified Hinkley retail distributor.

Several Hinkley Lighting products are protected under U.S. Patent and foreign patent, or patent pending. For current information regarding Hinkley Lighting's patent portfolio, please visit hinkleylighting.com.

©2017 Hinkley Lighting, Inc. All rights reserved in all copyrightable works.



Hinkley Lighting is a proud partner
of the American Lighting Association.

HINKLEY

L I G H T I N G

GLOBAL HEADQUARTERS

33000 Pin Oak Parkway | Avon Lake, Ohio 44012
T 440 653 5500 | F 440 653 5555 | hinkleylighting.com

SHOWROOM

Dallas Trade Mart 3210 | Dallas, Texas 75207



Connect with us | [#hinkleystyle](https://twitter.com/hinkleystyle)

2018 CATALOG

CAT18



\$25.00