



SAFETY, FACILITY AND EQUIPMENT IDENTIFICATION

www.BradyID.com



THE BRADY ADVANTAGE

When it comes to identification, safety and compliance, there's a clear advantage to working with Brady. We put our customers first in everything we do.

Our goal is to give you an unrivaled customer experience. We are relentlessly committed to performance and excellence - in our products, services and people.

Our products and solutions perform in ways that others simply can't match. Our people perform in ways that regularly exceed your expectations. And our focus and discipline work toward solid, long-term performance for our customers.

In short, Brady is the company you trust when performance matters most.



Learn more about the Brady Advantage by visiting www.BradyID.com



Don't Miss The Key Business Issues (page 4)

In depth Industry Overview pages address compliance and safety issues in:

- Lean Manufacturing, Maintenance and Reliability
- Lockout Tagout
- Arc Flash
- Hazard Communications
- Slips / Trips / Falls
- Spill Containment
- Voice / Data Communications
- Emergency Egress
- Hospital Facility Safety / TJC

NEW!

Check out some of Brady's NEW products and services!



BBP®31 Sign & Label Printer
Fast, Simple and Powerful Versatile!
(page 132)



ToughStripe® Floor Marking Tapes

The most durable floor marking tape!
(page 88)

NEW!



e-Learning Online Training Courses
Interactive course available 24 hours a day.
(page 258)

NEW!



Online Custom Design Tool

Design products to help meet your safety and compliance needs.
(page 251)

TABLE OF CONTENTS:

Key Business Issues	4	■
Safety Signs	22	■
Safety & Regulatory	58	■
Labels and Tags	66	■
Valve Tags	74	■
Pipe Markers	76	■
Lean/Visual Workplace	84	■
Security	100	■
Dispensers	102	■
Sign And Label Printers	104	■
Software And Laminators	156	■
Sorbents and Spill Control	160	■
Lockout/Tagout	178	■
Professional Safety Services	230	■
Index	234	■

Lean Manufacturing & Maintenance

www.BradyID.com/visualworkplace

CUT WASTE & STAY LEAN!

Manufacturers are often surprised to learn that only a small fraction of their activities actually add value for their customers. It's not uncommon that 90% or more of facility activities are considered waste!

A primary cause of waste is information deficits – employees lack the knowledge they need to do their jobs efficiently and effectively. This leads employees to waste valuable time asking, searching, waiting, or just giving up. A visual workplace eliminates questions, significantly enhancing worker productivity and efficiency.

In a visual workplace, information critical to the manufacturing process is built right into the physical environment. The visual devices are positioned at the point of use and are designed to be easily understood at a glance, thereby eliminating information deficits that lead to wasted time and motion.

“A visual workplace is a work environment that is self-ordering, self-explaining, self-regulating and self-improving – where what is supposed to happen does happen, on time, every time, because of visual solutions.”

Dr. Gwendolyn Galsworth, “Visual Workplace, Visual Thinking”
(page 87)

Lean Visuals Deliver Results

The effective implementation of visual systems can produce dramatic results:

- 15% increase in throughput
- 70% cut in materials handling
- 60% decrease in floor space
- 80% decrease in flow distance
- 68% reduction in rack storage
- 50% decrease in physical inventory time
- 96% decrease in defects


Source: www.visualworkplace.com, QMI/Visual-Lean Institute

www.BradyID.com/visualworkplace

- Application Ideas
- Product Solutions
- Articles & Whitepapers
- Best Practices
- Webcasts
- And Much More!

Visuals Sustain Continuous Improvement Efforts

Visuals are also critical to the success of kaizen continuous improvement programs. It is important to keep in mind that a continuously improving work environment is also a constantly changing work environment. Kaizen practitioners report that keeping employees informed of evolving best practices and preventing the natural tendency to revert back to old habits is a major hurdle. The use of visuals helps to ensure that new standards remain clearly visible, readily understood, and consistently adhered to by all employees.



Lean Manufacturing & Maintenance

www.BradyID.com/visualworkplace



How Can Lean Visuals Help You?

Visual devices play an important role in many lean concepts, including 5S, Standard Work, Quick Changeover, and Just-In-Time Inventory Management. The photos below illustrate just a few of the many applications for using visuals in lean manufacturing.

5S Workplace Organization



Standard Work





Quick Changeover



Kanban (Pull) Production



Visual Management



Lean Manufacturing & Maintenance

www.BradyID.com/visualworkplace

Equipment Reliability Made Visual

Lean manufacturers know that maintaining optimum equipment performance is critical, since they typically have less safety stock to rely on in the event of unexpected breakdowns. Equipment visuals such as those shown below are especially useful to those implementing autonomous, preventive and predictive maintenance programs.

Incorporating visuals into your reliability program can provide important benefits:

- Simplified operator-based care training
- Faster detection of operating abnormalities
- Quicker troubleshooting and root cause analysis
- Reduced stored inventory
- Fewer unplanned MRO purchases
- Improved safety and employee morale



BBP®31 Label Printer (page 132)

Labels made with MarkWare™ Software and a Brady Label Printer

Lubrication



Parts Management



PM Inspection



Predictive Maintenance



Equipment ID



! www.BradyID.com/visualworkplace

- Application Ideas
- Best Practices
- Product Solutions
- Webcasts
- Articles & Whitepapers
- And Much More!

Lean Manufacturing & Maintenance Product Solutions



Sign & Label Printers (page 104)

Brady label printers are essential tools for implementing a visual workplace, making it easy for you to create visuals onsite and on-demand.

- **GlobalMark® 2 Industrial Label Maker (page 142)**
- **BBP®31 Label Printer (page 132)**
- **BMP®71 Label Printer (page 104)**



MarkWare™ Lean Tools Software (page 84)

MarkWare Lean Tools software provides versatile drawing tools and hundreds of premade templates that speed the design of signs, labels and tags used in lean production, maintenance / reliability, warehouse and safety applications.




ToughStripe™ Floor Marking Tape (page 88)

ToughStripe® floor marking products are made with Brady's new B-514 polyester. ToughStripe products are ideal for marking aisles, passageways and storage locations, and pointing out important safety equipment and egress paths.



5S Marking Tapes (page 85)

Brady offers a wide range of products for marking floors, workbenches, tool boards and more. These products help to maintain order, identify hazards, and provide directional guidance.



Lean Communication Boards (page 88)

Lean information boards expand shop floor communications. Use to track key performance indicators, posting schedules and assignments and much more. They are durable yet lightweight and withstands industrial environments.



Sorbents (page 160)

SPC's extensive line of polypropylene and recycled cellulose-based sorbent products all provide for effective clean-up of spills and leaks throughout your facilities.



Irreversible Temperature Indicating Label

(www.BradyID.com/templabels)

Provide a permanent record of the highest temperature reached on a piece of equipment. When the equipment reaches a certain temperature, the white area on the label turns irreversibly black, giving clear proof of the highest temperature attained.

Lockout / Tagout

www.BradyID.com/lockouttagout

Lockout / Tagout: A Critical Safety Regulation

- **OSHA Focus** - Lockout is consistently the #1 most cited violation for general industry
- **Best Practice** - Recognized across many industries & markets
- **Saves Lives** - Properly implemented, lockout prevents an estimated 120 fatalities and 50,000 injuries annually
- **Reduces Costs** - Minimize costs from mishaps, including lost time, equipment, insurance and employee-related costs
- **Improves Productivity** - Minimizes equipment downtime

Brady is the global leader in Lockout / Tagout Solutions

Brady was first to respond to the new OSHA legislation in 1990, and has maintained its position as the leading Lockout solutions provider ever since. Today, Brady offers a comprehensive package for Lockout / Tagout compliance.



OSHA Regulation Summary:

OSHA 29 CFR §1910.147 The control of hazardous energy (lockout/tagout).

(a) Scope, application and purpose

(1) Scope. (i) This standard covers the servicing and maintenance of machines and equipment in which the unexpected energization or start up of the machines or equipment, or release of stored energy could cause injury to employees. This standard establishes minimum performance requirements for the control of such hazardous energy.

(2) Application. (i) This standard applies to the control of energy during servicing and / or maintenance of machines and equipment.

(3) Purpose. (i) This section requires employers to establish a program and utilize procedures for affixing appropriate lockout devices or tagout devices to energy sources, and to otherwise disable machines or equipment to prevent unexpected energization, start-up or release of stored energy in order to prevent injury to employees.

Why do you need lockout procedures?

- Documented, machine-specific energy control procedures are required by OSHA.
- Procedures serve as a check sheet to help employees avoid mistakes and reduce the risk of accidents and injuries.
- Procedures speed lockout activity, which in turn reduces downtime and improves operational productivity.



5-Steps To An Effective Lockout Program

Step 1: Develop Energy Control Policy/Program

The first step is to develop and document a lockout policy that identifies in detail the purpose and scope of your lockout program. It establishes the 'nuts and bolts' of your overall lockout program.



Step 2: Written, Equipment-Specific Lockout Procedures

Graphical lockout procedures, which include photos, are best practice in the industry today, as they provide clear, visually-intuitive instructions for employees to follow. Brady offers a number of options for creating these procedures:

- **Graphical Lockout Procedure-Writing Service (page 228)**
A turnkey, comprehensive service in which Brady develops your equipment-specific lockout procedures for you.
- **Lockout Pro™ Procedure-Writing Software (page 227)**
This software program has all the tools you need to create an effective, compliant energy control program with standardized procedures.
- **Online Custom Lockout Procedure Design Tool (page 227)** **NEW!**
Create your own custom lockout procedures at www.BradyID.com and print them on your own printer. Perfect solution for 25 or fewer procedures.

Step 3: Identify Energy Control Points

The third step is to locate and mark all energy control points, including valves, switches, breakers and plugs, with permanently placed labels or tags.

- **Energy Control Point Signs, Tags and Labels (page 222)**
Brady has a full line of energy source identification products.
- **Industrial Label Printers (page 132)**
Create your energy source identification with Brady's make-it-yourself high performance printing systems.



e-Learning now available at:
www.BradyID.com/elearning

Step 4: Training, Communication & Inspections

Brady offers interactive e-Learning training courses that provide comprehensive educations. Other communication products, including DVD's, handbooks and posters, are also available.

- **e-Learning Training Courses (page 225)** **NEW!**
Brady offers comprehensive online training courses for Authorized Workers and Corporate Safety Leaders.
- **Safety Training & Awareness Aids (page 224)**
Brady offers handbooks, posters, labels, videos and DVD programs that you can use to train your employees.

Step 5: Provide Proper Protective Products (page 176)

Brady offers a comprehensive line of lockout/tagout tools and devices, including nonconductive safety padlocks, lockouts for electrical circuit breaker switches, shutoff boxes, all types of valves, plugs, fuses, and more.



Comply with New Regulations, Increase Safety and Save Costs with Proper Identification.



There is a risk when working on live, energized electrical circuitry that can result in serious injury or death from a phenomenon known as Arc Flash. Arc Flash is a short circuit through the air that flashes between one live conductor to another conductor or to ground, causing a severe, explosive release of energy. It can be caused by a worker coming too close to a high-amp source with a conductive object, dropping a tool that makes contact with live components, breaks or gaps in wiring insulation or even poor maintenance practices. Arc Flash has the potential to generate extremely high heat, a forceful blast and intense light, caused by the rapid expansion of metallic components transforming to gas and molten particles in a fraction of a second. Experiencing an Arc Flash can cause severe injuries including loss of vision and hearing, third and fourth degree burns, along with the potential for severe electrical shock.

What Needs to be Labeled, And By Whom?

The NEC states that any of the following types of electrical equipment located in manufacturing and commercial establishments (other than dwelling occupancies) must be field marked with a warning label if subject to examination, adjustment, service or maintenance while energized:

- Switchboards
- Panelboards
- Industrial control panels
- Meter socket enclosures
- Motor control centers

The labeling requirement is the responsibility of the employer, not the manufacturer or installer of the equipment.



OSHA Regulation Summary:

Section 5(a)(1) of the Occupational Safety and Health Act

The Occupational Safety and Health Administration, OSHA, has become more involved in the Arc Flash issue and has begun citing employers for failure to protect workers from the dangers of Arc Flash incidents. While no specific standard exists regulating Arc Flash, OSHA utilizes Section 5(a)(1) of the OSHA Act, often referred to as the General Duty Clause, by basing enforcement actions on an employer's duty to "furnish to each of his employees employment and a place of employment which are free from recognized hazards that are causing or are likely to cause death or serious physical harm..." To provide guidance on best practices for protecting employees from Arc Flash hazards, OSHA refers employers to the NFPA 70E Standard, "Standard for Electrical Safety in the Workplace."

NFPA70E 2009 - "Standard for Electrical Safety in the Workplace"

NFPA 70E contains specific guidelines for working with energized equipment and includes information on safe work practices and maintenance requirements. Also included are suggested protective measures, such as equipment labeling and personal protective equipment (PPE) to ensure safe operations, along with methods for determining the severity of the potential hazard.

Numerous changes have been made in the new 2009 edition of NFPA 70E that include more explicit equipment labeling requirements, along with changes to PPE required for each hazard category. Generic warning labels are no longer considered sufficient enough to provide the necessary information a worker needs to protect themselves when working on energized equipment. NFPA 70E-2009 requires equipment to be field marked with a label containing the available incident energy or the required level of PPE.

The level of Arc Flash risk for each piece of equipment is dependent on a number of factors. Since the degree of risk may vary, even among similar equipment, labeling must be customized to represent the hazard present. Further, with the changes in PPE requirements found in NFPA 70E-2009, even hazard specific labeling created under the previous edition of NFPA 70E may be inadequate. For full details on the latest best practices, please refer to the 2009 edition of NFPA 70E.



Stock Labels (page 68)

Brady provides a variety of stock labels that are designed to help you display the required information. The vinyl check-box label shown here can be easily written on with pen or marker. An over-laminate can then be applied to protect the printing from harsh environmental conditions.

Custom Arc Flash Labels

Brady will print complete custom arc flash labels to your specific labeling requirements. For additional information, visit: www.bradyid.com/arcflash

Arc Flash Label Printing Systems (page 132)

Brady's Make-it-Yourself printing systems and software features Brady's performance 300 or 600 dpi thermal transfer printers optimized to print Brady media and your Arc Flash labeling requirements. The printers are designed to be a convenient, flexible and cost-effective way to create, modify and print labels on demand.



BBP®31 Sign & Label Printer (page 132)

- 2-touch printing – just walk up and print!
- Prints labels from ½” to 4” wide
- Stand alone or PC-connect operation
- Large touch-screen display with “touch and drag” moving and sizing
- Wizard-style apps for pipe ID, arc flash, and Right-To-Know chemical labels

High-Volume Labeling Solution - Bradyprinter™ PR Plus Printer

- Higher volume: up to 7,000 labels per day
- Heavier industrial environments
- Also ideal for rating plates, bar codes, general i.d., wire & cable marking, raised panel labels & more

Mid-Volume Labeling Solution - IP™ Series Printer

- Medium volume: up to 5,000 labels per day
- Just load, click, print. It's that simple.
- Lighter manufacturing environments
- Ideal for rating plates, industrial bar codes, general i.d., wire & cable marking, raised panel labels

Portable Labeling Solution - TLS 2200® Thermal Labeling System

- Print whatever, whenever.
- Auto label, size and text forming
- Also ideal for printing bar codes, general i.d., wire & cable marking, raised panel labels

Hazard Communications

www.BradyID.com/GHS

Hazard Communications:

More than 40 million workers in the US may routinely come into contact with hazardous chemicals while performing their jobs.

In many cases, the chemicals are no more dangerous than those at home. But in the workplace, exposure is likely to be greater, concentrations higher, and exposure time longer.

Reactions to chemical exposures range from slight skin, eye, or respiratory irritation to life-threatening cancers, blood diseases, and debilitating lung damage.

OSHA developed the Hazard Communication Standard (HCS) to protect workers from these dangerous exposures. The standard is based on a simple concept – employees have both a need and a right to know about the hazards and identities of the chemicals they are exposed to, and what they can do to protect themselves.



OSHA Regulation Summary:

OSHA 29 CFR 1910.1200 Hazard Communication

1910.1200(b)(1) This section requires chemical manufacturers or importers to assess the hazards of chemicals which they produce or import, and all employers to provide information to their employees about the hazardous chemicals to which they are exposed, by means of a hazard communication program, labels and other forms of warning, material safety data sheets, and information and training. In addition, this section requires distributors to transmit the required information to employers.

OSHA Focus – HazCom is the 2nd most frequently cited violation for general industry, following Lockout / Tagout

Best Practice – Recognized across many industries and markets

Saves Lives - Properly implemented, estimated to prevent more than 40 fatalities and 600 injuries and illnesses each year

Cost Reductions & Productivity Improvements – Estimated by OSHA to net a \$754 million savings to industry each year

Hazard Communication Program in 5 Steps:

- 1. Develop a comprehensive written Hazard Communication plan.**
This written plan outlines all of the sections of your organization's hazard communication program.
- 2. Inventory all chemicals.**
Develop a process to identify and log all hazardous chemicals in a central site, including record keeping and updates.
- 3. Establish & maintain a comprehensive Safety Data Sheet (SDS) program.**
All SDS's (previously known as Material Safety Data Sheets, or MSDS's) need to be collected and readily accessible to employees at all times on site.
- 4. Label all containers, pipes and tanks.**
Primary containers, secondary containers and pipe and storage pipes containing hazardous chemicals must be labeled according to the applicable hazard communication regulations and company-established programs.
- 5. Train and communicate with your workforce.**
All potentially affected employees must be fully trained according to the pertinent regulations and your hazard communication program.



Download the “Five Steps to Compliant Hazard Communication Program” at www.BradyID.com/GHS

Globally Harmonized System (GHS) for Classification and Labeling of Chemicals

NEW!

GHS is an acronym for the Globally Harmonized System. The GHS regulations are international regulations created by the United Nations for the Classification and Labeling of Hazardous Chemicals. The expectation is that the majority of countries globally will adopt and enforce most elements of the GHS through their regulatory agencies having jurisdiction for this public safety concern.

GHS Status in the U.S.


OSHA is expected to publish an updated Hazard Communications standard in September 2011, or shortly thereafter, that will incorporate the major elements of the GHS. A 3 year transitional period is expected to allow companies' time to fully implement the new standards in their facilities.

GHS Status around the World

The European Union is already well along the path to full implementation of GHS (referred to as CLP, Classification for Labelling & Packaging, by the EU), and countries in Asia are quickly following in its footsteps.



Visit www.BradyID.com/GHS for further updates and information on GHS.



Pre-Printed NFPA Diamond Identification (page 62)

Brady offers a variety of pre-printed write-on signs and labels for hazard communications, as well as training posters and aids.



Label Printers & Software for HazCom

(page 132)

Quickly design customized, professional-looking Right-To-Know signs and labels with Brady's advanced labeling software and printers.

GlobalMark®2 Sign & Label Printer (page 142)

This multi-color benchtop printer has a built-in plotter cutter and can create labels up to 4" wide. It even prints directly on magnets and tag stock.

MarkWare™ Facility Identification Software (page 156)

NEW! Markware™ 3.8 Software facilitates the creation and printing of GHS-compliant labels through Brady GlobalMark®2, PowerMark®, MiniMark™, and BMP®71 Label Printers.

Slips / Trips / Falls

www.BradyID.com/slipstripsfalls

10 Steps to Preventing Slips, Trips & Falls in the Workplace

OSHA is focusing on enforcing its standards associated with preventing slips, trips and falls.

According to OSHA, "Slips, trips, and falls constitute the majority of general industry accidents. They cause 15% of all accidental deaths, and are second only to motor vehicles as a cause of fatalities."



! OSHA Regulation Summary:

The OSHA Walking and Working Surfaces Standard: Subpart D 29 CFR 1910.21-30 identifies requirements intended to minimize Slips, Trips and Falls in the workplace.

The OSHA standards for walking/working surfaces apply to all permanent places of employment, except where only domestic, mining, or agricultural work is performed.



1. Assess your needs (page 230)

Brady's Slips/Trips/Falls Audit Service is a comprehensive evaluation of your facility's walking and working surfaces, with itemization of both required and recommended steps.




2. Mark aisles and passageways (page 88)

Brady's new ToughStripe® Floor Marking Tape provides superior durability, easy application and high visibility.



3. Provide traction on slippery surfaces (page 95)

Brady offers a variety of anti-skid floor tapes to provide traction.



4. Improve safety on stairs (page 93)

BradyGlo™ Anti-Skid Stairnosings products meet IBC, IFC and NFPA 2009 requirements for traction and visibility.

5. Mark emergency evacuation routes (page 37)

Brady offers BradyGlo™ UL-listed EXIT signs, handrail covers and a variety of other glow-in-the-dark products for visibility in lights-out conditions.

6. Post safety signage & labeling (page 94)

Mark your facility with stock fall protection signs and floor marking signs, or make your own signs and labels with a Brady label maker.



7. Warn of temporary hazards (page 99)

Mark temporary maintenance and janitorial hazards with Brady stands, barricade tapes, posts and chains.

8. Inspect scaffolds & ladders (page 75)

Brady's Scafftag products provide system, procedure and legal compliance.

9. Control and clean oil & spills (page 160)

Make sure your workroom floors are maintained in a clean and - so far as possible - dry condition with Brady's SPC Oil and Spill Containment & Clean-Up products.

10. Train your employees (page 60)


Brady offers high-impact, interactive CD-ROM training to educate employees slips, trips and falls prevention.



Did You Know?

20% of workplace injuries are caused by slips, trips & falls.

These result in an average of 11 days away from work and \$40,000 cost per incident.



Sorbents and Spill Control

www.BradyID.com/spc



Need a better way to absorb spills?

Brady's extensive line of SPC polypropylene and recycled cellulose-based sorbent products all provide for effective clean-up of spills and leaks throughout your facilities. SPC sorbents are specially fabricated to effectively absorb almost all oils, coolants, solvents, chemicals and water-based fluids.

SPC sorbents are far more efficient, safe and cost-effective than granular absorbents. Granular absorbents and clays, on the other hand:

- Are more expensive to dispose of
- As silica, are considered a health hazard by OSHA
- Provide limited chemical resistance
- Are messy and difficult to clean up
- Can introduce a slip hazard
- Can damage equipment and products



OSHA and EPA Regulation Summary:

Regulated by OSHA:

- Clean, dry workplace floors [29 CFR 1910.22(a)(2)]
- DOT-specified containers and suitable quantities of absorbents shall be kept available for response to spills [29 CFR 1910.120(j)(1)(vii)]

Regulated by EPA:

- Sorbent materials are one option for preventing oil spills from reaching waterways EPA: [40 CFR 112.7(c)(1)(vii)]
- EPA requires you to control sources of storm water runoff EPA: [40 CFR 122.26]
- EPA requires transporters to clean up any hazardous waste discharge EPA: [40 CFR 263.31]



Clean up oil and petroleum-based spills on land or water with specialized sorbents that don't absorb water.

Spill Prevention Control and Countermeasures Plan (SPCC):

The Spill Prevention Control and Countermeasures Plan (SPCC) is a facility-specific comprehensive description of a facility's containment and countermeasures that would prevent an oil spill from occurring as well as procedures to respond and clean up an oil spill that does occur. Driven by the EPA's Federal Water Pollution Control Act (as amended by the Clean Water Act), this ruling is designed to prevent discharges of oil and oil-related materials from reaching navigable waters and adjoining shorelines.

The SPCC Plan consists of three parts:

1. Operating procedures that prevent oil spills
2. Control measures to prevent a spill from reaching the environment
3. Countermeasures to contain, clean up, and mitigate the effects of an oil spill that reaches the environment





Re-Form Eco-Friendly Sorbents (page 162)

- Green to produce. Green in use.
- 50% more absorbent than oil-based polypropylene sorbents.
- Safe. Class A Fire Retardant.
- Also available in oil-only

Re-Form Granular Sorbents (page 168)

Just like other SPC sorbents, Re-Form™ Granular Sorbents provide superior absorbency so you can absorb more while using less.

- 100% recycled material
- Absorb oils, solvents, lubricants, coolants, water and most non-aggressive liquids on contact
- 1:1 absorbency ratio - absorbs its own weight in oil
- Leaves no stains or visible residue, and is virtually dust free

Universal Pads, Rolls and SOCS (page 164)

For most facility clean-up needs; oils, coolants, solvents and water-based fluids.

- MRO Plus™ Series
- MAXX Enhanced GP™ Series
- BattleMat™ - High Traffic
- Slikwik® Soc



Oil Only Pads, Rolls and SOCS (page 165)

Will not absorb water. Equally effective in soaking up petroleum-based solvents and paints, vegetable oils and other non-water soluble chemicals.

- ENV – MAXX Enhanced series
- SPC series
- Oil Plus series
- Oil Only Socs



Chemical Sorbent Pads & Rolls (page 166)

Chemical spill pads, absorbent mats and rolls from SPC are an economical option for even your toughest applications. Use SPC chemical sorbents to clean up drips and leaks that would otherwise put your safe facility at risk.



Portable Spill Kits (page 169)

SPC absorbent spill kits help you quickly and easily clean up spills of oils, solvents, coolants and other fluids. Brady offers a complete selection of SPC absorbent kits for plants, laboratories, work stations and construction sites.

Voice / Data Communications

www.BradyID.com/datacomm

Immediate identification of wires, cables and assets is essential.

Faster identification of network assets in order to perform moves, adds, and changes to the network while minimizing the interruption of network services to the businesses IT serves.

Identification of cables and panels specifically in areas of telecommunications, electrical, and datacomm is directly connected to performance. The ability for professionals to map a cables path across connected components is important in reducing the time taken to troubleshoot and locate networking problems.

Key Business Issues



ANSI/TIA/EIA 606 Standard Summary:

The standard specifies administration for a generic telecommunications cabling system that will support a multi-product, multi-vendor environment. It provides a uniform administration approach that is independent of applications, which may change several times throughout the life of the telecommunications infrastructure. It establishes guidelines for owners, end users, manufacturers, consultants, contractors, designers, installers and facilities administrators involved in the administration of the telecommunications infrastructure.

Use of this Standard is intended to increase the value of the system owner's investment in the infrastructure by reducing the labor expense of maintaining the system, extending the useful economic life of the system and providing effective service to users.



An Integrated, Seamless Solution.

Brady is the only company to provide an integrated and seamless solution to assist customers with their need to identify, document, and manage their cable and network assets. Stop following a tangle of cables and easily document every aspect of the network, including horizontal and backbone cables, hardware, assets, pathways, locations, air blown fiber, data center racks, users and more.



The Complete Voice / Data Comm Solution

Printing Systems (page 104)



IDXPert™ Handheld Labeler

- Print whatever, whenever.
- Auto label, size and text formatting
- Ideal for printing faceplate labels, cables, racks, public networks and general ID



BMP®71 Label Printer

- Prints on more than 30 types of label materials and at speeds of 1.5 labels per second
- Ideal for wire and cable markers, rating plates, tags, marking racks, bays, frames, slots, and other voice/data equipment.



BBP®31 Sign & Label Printer

- 2-touch printing - just walk up & print!
- Prints labels from 1/2" to 4" wide
- Stand alone or PC-connect operation
- Large touch-screen display with "touch and drag" moving and sizing

Materials (page 104)



Sleeves



Wrap-around



General ID



Flags / Tags

Software (page 156)

LabelMark™ Labeling Software

LabelMark™ software allows you to easily format cable, faceplate and closet labels. The software includes templates for all the Brady labels designed for your application, and has built in templates to automatically format 110 block and patch panels.

NetDoc™ Network Documentation

NetDoc® Network Documentation and Cable Management Software provides you with the tools you need to manage cabling, network, telephone and legacy connections. NetDoc® allows you to easily document horizontal and backbone cables, hardware, assets, pathways, locations, users and much more!



Services (page 157)

Whether installing your software for the first time or maintaining an existing database, NetDoc Customer Support is available when needed. Our Support Specialists are committed to getting you the fast accurate answers you need in order to be successful.



Emergency Egress and Exit Routes

www.BradyID.com/bradyglo

Support a quick and safe exit of your building during an emergency

The events of 9/11 have led to a greater focus on exit route markings and safety. This has also led to the increasing use of photoluminescent signs and exit pathway markings. The main reason is that photolum signs continue to remain visible even in electrical "lights-out" conditions.



2009 International Building Code:

Luminous egress path markings shall be required in most new and existing buildings having occupied floors located more than 75 feet above fire department vehicle access:


- All steps shall have a solid and continuous stripe applied for the full length.
- All handrails shall be marked with a solid and continuous stripe for the entire length.
- Doors through which occupants must pass shall be provided with luminous markings complying with sections 1027.6.1 – 1027.6.3.
- Photoluminescent or other luminous UL 924 listed exit signs shall be installed in accordance with section 411.7 (exit marking).

Regulated by OSHA: CFR 1910.33 – 39

- Every exit must be marked by a clearly visible sign with the word EXIT in plainly legible letters at least 6 inches high and with at least a 3/4" stroke width.
- Exit signs shall be illuminated either by internal or external means by a "reliable" light source giving a value of not less than 5 foot-candles on the illuminated surface.
- When the way to an exit is not readily apparent, signs or markings similar to exit signs shall be provided which also provide directional information. Where arrows are used, they shall be obvious as to the direction of the exit.
- Any door, passage or stairway that is not an exit but looks as though it could be an exit must be marked with a sign reading "NOT AN EXIT".
- An emergency action plan must be in writing, kept in the workplace and available to employees for review.

NFPA 101-2000 The Life Safety Code

- An employer who is in compliance with the Life Safety Code is also deemed to be in compliance with the corresponding OSHA section requirements.




Emergency Evacuation Marking (page 897)

Clearly mark emergency evacuation routes and exits.



Make Your Own Egress Signs (page 132)

BBP®31 Sign & Label Printer features 2-touch printing and can print labels from 1/2" to 4" wide.



Custom Glow Evacuation Maps

Print your evacuation maps on clear acetate and it glows in the dark. Contact Brady for more information.



The Joint Commission Compliance

In order to become or remain accredited by The Joint Commission (TJC), a hospital must provide safe, high quality health care. TJC references specific OSHA, NFPA, EPA and other regulations in its Environment of Care Crosswalk, stressing the requirement to comply with these important safety rules.

The Joint Commission provides three standards chapters related to Environment of Care management:

- Environment of Care (EC) chapter
- Emergency Management (EM) chapter
- Life Safety (LS) chapter



OSHA Regulation Summary:

OSHA CFR 1910.147 The Control of Hazardous Energy (Lockout/Tagout)

Machine-specific lockout/tagout procedures are required for equipment that has more than one energy source, as well as for equipment that has a single energy source in most conditions.

Brady Graphical Lockout Procedure Service (page 228)

An on-site comprehensive service in which Brady engineers come to the facility and create equipment-specific procedures. This service can be completed in a matter of days – saving hospitals significant time and money on lockout compliance! The service includes:

- On-site equipment assessment performed by Brady engineers
- Compliant, easy-to-follow procedures for each piece of equipment
- Installation of laminated procedures and energy source ID tags directly on equipment
- Electronic and hard copies of all machine-specific LOTO procedures
- Employee training for updating and creating additional procedures
- Recommended lockout/tagout product list based on facility needs




Did You Know?

The US Department of Veterans Affairs has confirmed that its hospital facilities are required to comply with OSHA standards. VA recognizes that equipment-specific lockout procedures will improve safety. It has directed its medical centers to develop specific SOP's for de-energizing and/or releasing stored energy in the identified energized equipment.

Additional Brady Services (page 229)

Brady's hospital identification services and products can also help hospitals meet TJC requirements for:

- Labeling of Hazardous Chemicals
- Confined Spaces
- Safety Signage and Labeling
- Slips/Trips/Falls Prevention
- Emergency Egress
- And more!



What Equipment Requires Lockout Procedures?

A typical hospital has 100 to 300 or more pieces of equipment that require written procedures!

Common hospital equipment that requires lockout procedures:

- Boilers
- Generators
- Vacuum pumps
- And more!
- Chillers
- Sterilizers
- Air handlers

About Safety Signs

www.BradyID.com

Safety Signs

Brady signs feature bright colors, bold text and intuitive pictographs to ensure that the communication is highly visible and easily understood. The signs are compliant with the latest standards and regulations, and designed to withstand even the harshest industrial environments.

Can't find the sign you need?

Use the Sign Legend Index on page 234 to quickly and easily locate a specific sign within this catalog.

Or visit www.BradyID.com to view more than 8,000 different signs for safety, maintenance and facility identification.

Example Legend Listing:



FG - 7 x 10 - 70885
 PL - 7 x 10 - 22433
 PL - 10 x 14 - 22434
 SS - 7 x 10 - 84571

Material Size Catalog #

ASME (ANSI Z535) SIGN HEADER GUIDE

ASME (ANSI Z535) and the Occupational Safety and Health Administration (OSHA 1910.145) Specifications for Accident Prevention Signs require the use of Safety Signs to indicate and define specific hazards that, without identification, may lead to accidental injury to workers and/or the public or to property damage.

DANGER	WARNING	CAUTION	NOTICE	SAFETY FIRST. THINK, BE CAREFUL
Indicates an immediate hazard; a hazard capable of producing irreversible damage or injury.	Indicates a potentially hazardous situation which, if not avoided, could result in death or serious injury.	Indicates a potentially hazardous situation; a hazard capable of resulting in severe but not irreversible injury or damage.	Provides information of a general type in order to avoid confusion or misunderstanding.	Includes notices of general practice and rules relating to health, first aid, medical equipment, sanitation, housekeeping and general safety.



Eco-Friendly Sign Material

Eco-Friendly Safety Signs offer an eco-friendly alternative to traditional plastic safety signs. Brady offers three different material options for eco-friendly signs: paper, plastic and pressure-sensitive.

B-586 Paper Signs

- Made of 10% post consumer waste
- Signs are 100% recyclable
- Suitable for indoor applications
- Stable, rigid paper material
- Material is 3.5mm thick
- Available for popular safety sign legends, in sizes 10"x14" and 7"x10"

B-563 Plastic Signs

- Made of 70% post consumer waste
- Can withstand outdoor conditions for 3-5 years
- Material is 0.55mm thick
- Available for popular safety sign legends, in sizes 10"x14" and 7"x10"

B-558 Pressure Sensitive Signs

- Made of 20% pre-consumer waste
- Material is 0.004 in. thick
- 3-5 year outdoor durability
- Permanent adhesive backing
- Available for popular safety sign legends, in sizes 10"x14" and 7"x10"

Visit www.BradyID.com to view all available Eco-Friendly signs.



Safety Sign Material and Price Guide

www.BradyID.com

Stock Sign Materials

B-120 - Premium Fiberglass Signs (FG)

- Made of our highest quality, longest lasting sign material
- Will not peel or fade
- Guaranteed for 15 years
- Ideal for outdoors or harsh environments

B-555 - Aluminum Signs (AL)

- Superior abrasion and chemical resistance, indoors or out
- Protected graphics keep message clear
- Weather and sunlight resistant
- Stands up to spills, washdowns and cleanings

B-401 - Plastic Signs (PL)

- Economically priced, perfect for light duty or temporary use
- Protected graphics for durability
- 1 to 2 year outdoor life
- Over 2000 stock legends

B-302 - High Performance Polyester Signs (SS)

- Bright graphics on flexible material, sticks to almost any shape or surface. Permanent adhesive holds where others fail
- Lasts up to 8 years outdoors, longer indoors
- Stands up to repeated spills and cleanings

Stock Sign Material Specifications

Brady offers a sign material for virtually every application. Whether the sign is used indoors or outdoors, in mild or harsh environments, we have the material to match your application. Select the right sign for your application dependent upon the factors listed in the table below.

Material Descriptions	Protected Graphics	Self-Sticking	Indoor(I) Outdoor(O)	Average Outdoor Durability (Yrs)	Chemical Resistance	Abrasion Resistance	Upper Temp Limit
B-302 High Performance Polyester	Yes	Yes	I/O	8	Excellent	Excellent	230° F, 100°C
B-946 Self-Sticking Vinyl	No	Yes	I/O	5	Fair	Good	180°F, 82°C
B-997 BradyLite® Reflective Vinyl	No	Yes	I/O	4-6	Good	Good	200°F, 93°C
B-324 BradyGlo™ Polyester	No	Yes	I	-	Good	Good	230°F, 110°C
B-928 Write-On Vinyl	No	Yes	I/O	2	Good	Good	176°F, 93°C
B-347 BradyGlo™ Plastic	No	No	I	-	Good	Good	194°F, 110°C
B-401 Plastic	Yes	No	I/O	2	Good	Good	150°F, 66°C
B-793 Polystyrene	No	No	I/O	1-3	Poor	Good	165°F, 74°C
B-836 Temporary Sign Fluted Polypropylene	No	No	I/O	1	Good	Good	130°F, 54°C
B-450 Polyethylene Plastic	No	No	I	3-5	Good	Good	180°F, 82°C
B-382 BradyGuard™ Fiberglass	Yes	No	I/O	8	Good	Good	175°F, 79°C
B-1 Engraved Plastic	No	No	I/O	5-8	Good	Good	193°F, 89°C
B-555 Aluminum	Yes	No	I/O	5-8	Excellent	Excellent	212°F, 100°
B-959 Reflective Aluminum	No	No	I/O	5-8	Good	Good	196°F, 80°
B-995 Diamond-Grade™ Reflective Aluminum	No	No	O	7	Good	Good	200°F, 93°C
B-811 Magnetic Vinyl	No	No	O	2-4	Good	Good	158°F, 70°C
B-120 Premium Fiberglass	Yes	No	I/O	15	Excellent	Excellent	190°F, 88°C
B-140 BradyLam™ Fiberglass	Yes	No	I/O	15	Excellent	Excellent	230°F, 110°C
B-320 BradyLex™ Fiberglass	Yes	No	I/O	8	Good	Good	175°F, 79°C

Stock Sign Pricing

MATERIAL	3 x 3	3 1/2 x 5	5 x 14	7 x 10	10 x 14	12 x 18	14 x 3 1/2	14 x 20	24 x 4	24 x 18
B-120 - Premium Fiberglass (FG)	\$1.52			\$13.19	\$23.93	\$33.47	\$11.30		\$15.10	\$62.16
B-555 - Aluminum (AL)				\$11.87	\$19.74					
B-401 - Plastic (PL)				\$9.81	\$13.90			\$34.10		
B-302 - High Performance Polyester (SS)		\$2.24	\$8.20	\$8.38	\$11.53					
B-324 - BradyGlo™ Polyester			\$13.64	\$13.64	\$27.64					
B-347 - BradyGlo™ Plastic				\$23.74	\$54.04					

MATERIAL	6 x 12	12 x 12	18 x 12	18 x 18	24 x 18	24 x 24	24" Triangle	30" Triangle	30" Diameter	30 x 30	36 x 36
Reflective Aluminum (B-959)	\$22.77	\$32.29	\$44.17	\$63.75	\$84.66	\$111.61	\$87.18	\$134.20	\$159.47	\$159.47	\$231.93

Safety Signs

www.BradyID.com

Admittance Signs

Safety Signs



FG - 10 x 14 - 69097
AL - 10 x 14 - 40646



FG - 7 x 10 - 70885
PL - 7 x 10 - 22433
PL - 10 x 14 - 22434
SS - 7 x 10 - 84571



AL - 10 x 14 - 40676
FG - 10 x 14 - 47008
PL - 10 x 14 - 22112
SS - 10 x 14 - 84096



PL - 10 x 14 - 22114



FG - 7 x 10 - 47152
AL - 10 x 14 - 40674



AL - 10 x 14 - 95363



FG - 10 x 14 - 95373
PL - 10 x 14 - 95372



AL - 10 x 14 - 95380



SS - 10 x 14 - 84033



FG - 10 x 14 - 69101



AL - 7 x 10 - 40663



FG - 10 x 14 - 70375
AL - 10 x 14 - 40666



FG - 7 x 10 - 45470
FG - 14 x 20 - 45472
AL - 7 x 10 - 40667
AL - 10 x 14 - 40668
SS - 3 1/2 x 5 - 84082
SS - 7 x 10 - 84083



PL - 7 x 10 - 25532



AL - 7 x 10 - 40669
AL - 10 x 14 - 40670
FG - 14 x 20 - 71580
PL - 7 x 10 - 22105
PL - 10 x 14 - 22106
SS - 3 1/2 x 5 - 87751
SS - 7 x 10 - 84085
SS - 10 x 14 - 84086



AL - 10 x 14 - 40658
PL - 10 x 14 - 22094



FG - 10 x 14 - 69193
AL - 10 x 14 - 40656
PL - 10 x 14 - 22092
SS - 3 1/2 x 5 - 87755
SS - 7 x 10 - 84066



PL - 14 x 10 - 22432
SS - 10 x 7 - 84569
SS - 14 x 10 - 84570



PL - 10 x 14 - 60536



AL - 10 x 14 - 43381
FG - 10 x 14 - 73451
PL - 10 x 14 - 25804



FG - 14 x 20 - 73408
PL - 10 x 14 - 22430
SS - 7 x 10 - 84567
SS - 10 x 14 - 84568



FG - 14 x 20 - 71229
AL - 10 x 14 - 40750
PL - 10 x 14 - 22186
SS - 7 x 10 - 84183




AL - 10 x 14 - 40754
FG - 10 x 14 - 71389
SS - 10 x 14 - 84188
PL - 10 x 14 - 22190



FG - 10 x 14 - 70220
AL - 10 x 14 - 40742
SS - 7 x 10 - 84175
PL - 10 x 14 - 22178



FG - 14" x 20" - 95458



AL - 10 x 14 - 40772
FG - 10 x 14 - 70833
PL - 10 x 14 - 22208
SS - 10 x 14 - 84213




AL - 10 x 14 - 40780



AL - 10 x 14 - 40797
FG - 14 x 20 - 71216
AL - 7 x 10 - 40796
PL - 10 x 14 - 22233




AL - 7 x 10 - 40791
FG - 5 x 14 - 70736
PL - 7 x 10 - 22227



AL - 10 x 14 - 40788



FG - 10 x 14 - 69096
PL - 10 x 14 - 22218



AL - 10 x 14 - 40778
PL - 10 x 14 - 22214



FG - 10 x 14 - 71293
FG - 14 x 20 - 71288
AL - 10 x 14 - 40813
PL - 10 x 14 - 22249



FG - 14 x 20 - 71282



SS - 3 1/2 x 10 - 84211



AL - 10 x 14 - 40815

Admittance Signs



AL - 10 x 14 - 41102
 FG - 10 x 14 - 70667
 PL - 10 x 14 - 22538
 SS - 7 x 10 - 84732
 SS - 10 x 14 - 84733



AL - 10 x 14 - 40728
 FG - 10 x 14 - 47330
 FG - 14 x 20 - 75510
 PL - 7 x 10 - 22163
 PL - 10 x 14 - 22164
 SS - 10 x 14 - 84156



AL - 10 x 14 - 40708
 FG - 10 x 14 - 47327
 PL - 10 x 14 - 22144
 SS - 10 x 14 - 84132



FG - 10 x 14 - 69477



PL - 10 x 14 - 95247



AL - 7 x 10 - 40705
 AL - 10 x 14 - 40706
 FG - 7 x 10 - 73476
 FG - 10 x 14 - 70602
 PL - 7 x 10 - 22141
 PL - 10 x 14 - 22142
 SS - 7 x 10 - 84129
 SS - 10 x 14 - 84130



AL - 10 x 14 - 95318



FG - 10 x 14 - 95278
 AL - 10 x 14 - 60510
 PL - 10 x 14 - 60539
 SS - 10 x 14 - 60578



AL - 10 x 14 - 43479



AL - 10 x 14 - 84907



AL - 7 x 10 - 95255
 AL - 10 x 14 - 43478
 PL - 7 x 10 - 95256



FG - 7 x 17 - 95284



AL - 10 x 14 - 40624
 AL - 7 x 10 - 40623
 FG - 7 x 10 - 75444
 FG - 10 x 14 - 47093
 SS - 7 x 10 - 84008
 PL - 7 x 10 - 22059
 PL - 10 x 14 - 22060



AL - 7 x 10 - 40625
 AL - 10 x 14 - 40626
 PL - 10 x 14 - 22062
 SS - 7 x 10 - 84010




FG - 10 x 14 - 69103



SS - 7 x 10 - 84006

Alert Signs



PL - 7 x 10 - 21709
 SS - 7 x 10 - 83660
 SS - 3 1/2 x 5 - 83883



AL - 10 x 14 - 46754
 FG - 10 x 14 - 62813
 PL - 7 x 10 - 21801
 PL - 10 x 14 - 26576
 SS - 7 x 10 - 83754



AL - 10 x 14 - 46741
 AL - 7 x 10 - 46464
 PL - 10 x 14 - 26563
 SS - 3 1/2 x 5 - 83916
 SS - 7 x 10 - 83741



AL - 10 x 14 - 46674
 PL - 7 x 10 - 21713
 PL - 10 x 14 - 26534



AL - 10 x 14 - 46748
 FG - 7 x 10 - 62545
 FG - 10 x 14 - 62807
 PL - 7 x 10 - 21795
 PL - 10 x 14 - 26570




PL - 10 x 14 - 26572



AL - 10 x 14 - 46819
 FG - 10 x 14 - 62866
 PL - 7 x 10 - 21866
 PL - 10 x 14 - 26591
 SS - 3 1/2 x 5 - 83954
 SS - 7 x 10 - 83839



PL - 10 x 14 - 26560
 SS - 10 x 14 - 60572




SS - 3 1/2 x 5 - 83956
 SS - 7 x 10 - 83841



SS - 3 1/2 x 5 - 83911
 SS - 7 x 10 - 83736



AL - 7 x 10 - 46643
 SS - 3 1/2 x 5 - 83898




SS - 3 1/2 x 5 - 83907




SS - 3 1/2 x 5 - 83912



AL - 10 x 14 - 46735
 PL - 10 x 14 - 26557



SS - 3 1/2 x 5 - 83902



SS - 3 1/2 x 5 - 83900



PL - 7 x 10 - 21806



PL - 7 x 10 - 21807



PL - 7 x 10 - 21700

Safety Signs

www.BradyID.com

Safety Signs

ANSI Z535 Safety Signs



FG - 10 x 7 - 45009



PL - 14 x 10 - 45072



SS - 10 x 7 - 45159



SS - 10 x 7 - 45117



FG - 10 x 7 - 141913
 FG - 14 x 10 - 141908
 SS - 10 x 7 - 141914
 SS - 14 x 10 - 141909
 AL - 10 x 7 - 141915
 AL - 14 x 10 - 141910
 B-946 - 10 x 7 - 141916
 B-946 - 14 x 10 - 141911
 PL - 10 x 7 - 141917
 PL - 14 x 10 - 141912



AL - 10 x 7 - 48983



FG - 14 x 10 - 45018



PL - 14 x 10 - 45096

ANSI Z535

The ANSI Z535 Committee on Safety Signs was created to update the standards of safety signage. Its primary purpose is to develop standards for the design, application and use of signs, colors, and symbols intended to identify and warn against specific hazards and for other accident prevention purposes. The new recommended format is intended to provide a safety alert message that is clearly and rapidly understood.

Blank Signs & Pre-Printed Headers



AL - 7 x 10 - 42953
 FG - 7 x 10 - 76063
 FG - 10 x 14 - 47000
 FG - 14 x 20 - 76034
 FG - 20 x 28 - 76036
 AL - 10 x 14 - 42954
 PL - 3 1/2 x 5 - 25963
 PL - 5 x 7 - 25960
 PL - 7 x 10 - 25376
 PL - 10 x 14 - 25377
 SS - 7 x 10 - 88948
 SS - 10 x 14 - 88949



AL - 10 x 14 - 42952
 FG - 10 x 14 - 76040
 FG - 14 x 20 - 76045
 FG - 20 x 28 - 76050
 PL - 7 x 10 - 25374
 PL - 10 x 14 - 25375
 SS - 10 x 14 - 88947



AL - 7 x 10 - 42941
 AL - 10 x 14 - 42942
 FG - 10 x 14 - 47014
 FG - 14 x 20 - 76021
 PL - 10 x 14 - 25365
 SS - 7 x 10 - 88932
 SS - 10 x 14 - 88933
 B101 - 10 x 14 - 65266



AL - 7 x 10 - 42937
 AL - 10 x 14 - 42938
 FG - 10 x 14 - 47004
 FG - 7 x 10 - 76009
 PL - 10 x 14 - 25361
 SS - 7 x 10 - 88925
 SS - 10 x 14 - 88926
 B-101 - 10 x 14 - 65262
 B-836 - 10 x 14 - 78066



AL - 7 x 10 - 42933
 AL - 10 x 14 - 42934
 FG - 7 x 10 - 76005
 FG - 10 x 14 - 47002
 PL - 10 x 14 - 25357
 SS - 7 x 10 - 88918
 SS - 10 x 14 - 88919
 B-101 - 10 x 14 - 65264



FG - 14 x 20 - 69810




AL - 10 x 14 - 42950
 PL - 10 x 14 - 25373




SS - 2 1/4 x 9 - 88922

Braille (ADA) Signs

- Signs meet ADA requirements and CABO/ANSI A117.1 specifications for identifying permanent rooms
- Made of B-81 rigid plastic with non-glare matte finish
- Includes two strips of double-faced tape



B-81-Wht/Blk-8 x 8 - 70110



B-81-Wht/Blk-8 x 8 - 70109



B-81-Wht/Blk-2 x 8 - 70115
 B-81-Wht/Br-2 x 8 - 70141


All of these signs feature a true dome-shaped Braille dot to meet new CABO/ANSI A117.1 specifications.




B-81-Wht/Blk-6 x 6 - 70123
 International Symbol of Accessibility



B-81-Wht/Blk-8 x 8 - 70103
 B-81-Wht/Br-8 x 8 - 70129




B-81-Wht/Blk-8 x 8 - 73400




B-81-Wht/Blk-8 x 8 - 70102

Sign materials and pricing can be found on page 23.


Bilingual & Spanish Signs



Bilingual
 FG - 20 x 14 - 39512
 AL - 14 x 10 - 38112
 PL - 14 x 10 - 38612
 SS - 14 x 10 - 90667
 Spanish Only
 PL - 10 x 14 - 38662



Bilingual
 FG - 20 x 14 - 39514
 AL - 14 x 10 - 38114



Bilingual
 FG - 20 x 14 - 39961
 SS - 14 x 10 - 90674



Bilingual
 PL - 14 x 10 - 38937
 SS - 14 x 10 - 90807



Bilingual
 PL - 14 x 10 - 39084
 SS - 14 x 10 - 90799




Bilingual
 PL - 14 x 10 - 39085



Bilingual
 PL - 14 x 10 - 39086
 SS - 14 x 10 - 90818



Bilingual
 AL - 14 x 10 - 38430
 PL - 14 x 10 - 38942
 SS - 14 x 10 - 90809



Bilingual
 AL - 14 x 10 - 38175
 PL - 14 x 10 - 38679
 SS - 14 x 10 - 90797
 Spanish Only
 FG - 10 x 14 - 39601



Bilingual
 FG - 20 x 14 - 39506
 AL - 14 x 10 - 38106
 PL - 14 x 10 - 38606
 SS - 14 x 10 - 90793




Bilingual
 AL - 14 x 10 - 38587
 PL - 14 x 10 - 39087
 SS - 14 x 10 - 90803



Bilingual
 AL - 14 x 10 - 38104
 PL - 14 x 10 - 38604



Bilingual
 FG - 20 x 14 - 39876
 AL - 14 x 10 - 38478
 PL - 14 x 10 - 38990



Bilingual
 PL - 14 x 10 - 38767



Bilingual
 AL - 14 x 10 - 38481
 PL - 14 x 10 - 38993



Bilingual
 PL - 14 x 10 - 38994



Bilingual
 FG - 14 x 20 - 39821
 PL - 10 x 14 - 38933

Safety Signs

www.BradyID.com

Safety Signs

Biohazard, Chemical & Hazardous Materials



SS - 3 1/2 x 5 - 89170
SS - 7 x 10 - 85553



SS - 5 x 3 1/2 - 89169



AL - 10 x 14 - 41314



FG - 10 x 14 - 70372
PL - 10 x 14 - 25441
SS - 10 x 14 - 84398



FG - 10 x 14 - 70373



AL - 10 x 14 - 40876
FG - 10 x 14 - 70240
PL - 10 x 14 - 22312
SS - 10 x 14 - 84352



SS - 10 x 14 - 84362



SS - 10 x 14 - 85182



FG - 10 x 14 - 72246
AL - 10 x 14 - 43244
PL - 10 x 14 - 25667
SS - 7 x 10 - 85183
SS - 10 x 14 - 85184



FG - 10 x 14 - 72230
AL - 10 x 14 - 43238
PL - 10 x 14 - 25661
SS - 10 x 14 - 85176



FG - 10 x 14 - 70266
AL - 10 x 14 - 43006
PL - 10 x 14 - 25429
SS - 7 x 10 - 84375
SS - 10 x 14 - 84376



SS - 7 x 10 - 85458



FG - 10 x 14 - 47206
PL - 10 x 14 - 22295
SS - 7 x 10 - 84326
SS - 10 x 14 - 84327



SS - 7 x 10 - 84387



FG - 10 x 14 - 73489
SS - 7 x 10 - 84345



FG - 10 x 14 - 70258
AL - 10 x 14 - 40888
PL - 10 x 14 - 22324
SS - 10 x 14 - 84368




FG - 10 x 14 - 69043



SS - 10 x 14 - 84358



FG - 10 x 14 - 72408
SS - 10 x 14 - 84356



FG - 20 x 14 - 74520
PL - 14 x 10 - 22722



AL - 10 x 14 - 40906



FG - 10 x 14 - 69765



FG - 10 x 14 - 72473



AL - 7 x 10 - 43013
AL - 10 x 14 - 43014
FG - 10 x 14 - 69275



SS - 7 x 10 - 84371



AL - 10 x 14 - 43246
PL - 10 x 14 - 25669



AL - 10 x 14 - 42646
PL - 10 x 14 - 25069
SS - 10 x 14 - 88360



SS - 3 1/2 x 5 - 85451



FG - 14 x 20 - 70423
AL - 10 x 14 - 40892



AL - 10 x 14 - 43487
PL - 10 x 14 - 25910

Biohazard, Chemical & Hazardous Materials (continued)



AL - 10 x 14 - 40882
SS - 7 x 10 - 84361



FG - 10 x 14 - 75639
SS - 7 x 10 - 85167



SS - 7 x 10 - 85179



SS - 10 x 14 - 86034



FG - 10 x 14 - 73418
AL - 7 x 10 - 42715
PL - 7 x 10 - 25138



FG - 10 x 14 - 70356
AL - 7 x 10 - 43323
PL - 7 x 10 - 25746



FG - 10 x 14 - 70317
AL - 7 x 10 - 43322
PL - 7 x 10 - 25745



FG - 10 x 14 - 69407
SS - 7 x 10 - 84467



SS - 7 x 10 - 84463



FG - 7 x 10 - 72546



AL - 10 x 14 - 95007



AL - 10 x 14 - 60350
SS - 7 x 10 - 43983



AL - 10 x 14 - 30671
SS - 7 x 10 - 30674



AL - 10 x 14 - 43496



FG - 14 x 20 - 69005



SS - 7 x 10 - 60563



AL - 10 x 14 - 41284



FG - 10 x 14 - 70374



AL - 10 x 14 - 43499



AL - 10 x 14 - 41262
PL - 7 x 10 - 22697
SS - 7 x 10 - 85382



FG - 14 x 20 - 69291



FG - 10 x 14 - 47117
PL - 10 x 14 - 22273
SS - 10 x 14 - 84298



SS - 7 x 10 - 84301



FG - 10 x 14 - 69042



AL - 7 x 10 - 40846
FG - 10 x 14 - 69408
SS - 7 x 10 - 84313



FG - 7 x 17 - 69308



FG - 7 x 17 - 69264



FG - 7 x 17 - 95277



FG - 7 x 17 - 69409

Safety Signs

www.BradyID.com

Safety Signs

Confined Space

OSHA Requirements

Permit Required Confined Space, Do Not Enter 1910.146(c)(2)
Exposed employees must be informed of the existence and location of and the danger posed by permit-required confined spaces through the posting of danger signs or by any other equally effective means. A sign reading "DANGER – PERMIT – REQUIRED CONFINED SPACE, DO NOT ENTER" or using other similar language satisfies the requirement.

Accident Prevention 1910.145(c)(2)
Caution signs shall be used only to warn against potential hazards or to caution against unsafe practices. All employees shall be instructed that caution signs indicate a possible hazard against which proper precaution should be taken.



AL - 7 x 10 - 95014
AL - 10 x 14 - 60506
FG - 10 x 14 - 95013
FG - 7 x 10 - 95012
PL - 7 x 10 - 95015
PL - 10 x 14 - 60535
SS - 7 x 10 - 95018
SS - 10 x 14 - 60569



AL - 7 x 10 - 43517
AL - 10 x 14 - 43518
FG - 7 x 10 - 65948
FG - 10 x 14 - 65817
PL - 7 x 10 - 25920
PL - 10 x 14 - 25921
SS - 3 1/2 x 5 - 87768
SS - 7 x 10 - 65950
SS - 10 x 14 - 65949



FG - 7 x 10 - 70248
FG - 10 x 14 - 70249
AL - 7 x 10 - 40988
AL - 10 x 14 - 40989
PL - 7 x 10 - 22424
PL - 10 x 14 - 22425
SS - 3 1/2 x 5 - 87748
SS - 7 x 10 - 84562
SS - 10 x 14 - 84563



FG - 7 x 10 - 87674
FG - 10 x 14 - 87675
AL - 7 x 10 - 19194
AL - 10 x 14 - 19200
PL - 7 x 10 - 19193
PL - 10 x 14 - 19199
SS - 10 x 14 - 19197



SS - 2 14 x 2 14 - 84551



AL - 7 x 10 - 40997
AL - 10 x 14 - 40998



AL - 10 x 14 - 40994



SS - 14 x 10 - 84564




FG - 10 x 14 - 47018
AL - 10 x 14 - 40972
PL - 7 x 10 - 22407
PL - 10 x 14 - 22408
SS - 7 x 10 - 84537
SS - 10 x 14 - 84538



AL - 10 x 14 - 40964
FG - 7 x 10 - 47061
FG - 10 x 14 - 47050
PL - 7 x 10 - 22399
PL - 10 x 14 - 22400
SS - 7 x 10 - 84529
SS - 10 x 14 - 84530



FG - 10 x 14 - 74581
AL - 10 x 14 - 40970
PL - 10 x 14 - 22406
SS - 10 x 14 - 84536



FG - 20 x 14 - 65917
PL - 14 x 10 - 22417
SS - 14 x 10 - 84547



AL - 10 x 14 - 41191
PL - 10 x 14 - 22627



PL - 10 x 14 - 25611



PL - 10 x 14 - 22419
SS - 10 x 14 - 84557



PL - 10 x 14 - 22416
SS - 10 x 14 - 84546



PL - 10 x 14 - 22404
SS - 10 x 14 - 84534

Door Signs



FG - 10 x 14 - 47113
AL - 10 x 14 - 41076
PL - 10 x 14 - 22512
SS - 7 x 10 - 84699
SS - 10 x 14 - 84700



SS - 3 1/2 x 10 - 84750



PL - 10 x 14 - 22510
SS - 10 x 14 - 84698




FG - 10 x 14 - 70466
AL - 10 x 14 - 41080
PL - 7 x 10 - 22515
PL - 10 x 14 - 22516
SS - 7 x 10 - 84706
SS - 10 x 14 - 84707



AL - 10 x 14 - 41094
PL - 10 x 14 - 22530
SS - 7 x 10 - 84720
SS - 10 x 14 - 84721



FG - 10 x 14 - 75971
PL - 7 x 10 - 22560
SS - 7 x 10 - 84770



SS - 7 x 10 - 84768



SS - 7 x 10 - 84751

Sign materials and pricing can be found on page 23.

Electrical Hazard



AL - 7 x 10 - 42753



SS - 3 x 3 - 89153



FG - 10 x 10 - 69190
SS - 10 x 10 - 88497



SS - 3 x 3 - 89152



OSHA Requirements

High Voltage 1910.305(b)(3)

Covers for boxes shall be permanently marked "High Voltage." The marking shall be on the outside of the box cover and shall be readily visible and legible.

Access Area Marking 1910.303(g)(1)

Sufficient access and working space must be provided and maintained about all electric equipment to permit ready and safe operation and maintenance of the equipment.



FG - 7 x 10 - 71565
FG - 10 x 14 - 47005
AL - 7 x 10 - 43109
AL - 10 x 14 - 43110
PL - 10 x 14 - 25533
SS - 7 x 10 - 84876
SS - 10 x 14 - 84877



AL - 10 x 14 - 43477
PL - 10 x 14 - 25900
SS - 10 x 14 - 60580



FG - 14 x 20 - 75590
SS - 2 1/4 x 4 1/2 - 89173
SS - 3 1/2 x 5 - 84875



B-324 - 7 x 10 - 73540



FG - 10 x 14 - 45471
AL - 10 x 14 - 40668
PL - 10 x 14 - 22104
SS - 10 x 14 - 84084



AL - 10 x 14 - 43118



AL - 10 x 14 - 19938
PL - 7 x 10 - 19931
SS - 10 x 14 - 19935



Use 1" numbers:
FG - 10 x 14 - 69025
AL - 10 x 14 - 43130
PL - 10 x 14 - 25553
SS - 7 x 10 - 84903




Use 2" numbers:
SS - 7 x 10 - 84927



SS - 7 x 10 - 84859
SS - 10 x 14 - 84860



FG - 10 x 14 - 71545
SS - 7 x 10 - 84068
SS - 10 x 14 - 84069



SS - 3 1/2 x 10 - 84963



FG - 7 x 17 - 95287



FG - 14 x 20 - 69024
AL - 10 x 14 - 43124
PL - 7 x 10 - 25546
PL - 10 x 14 - 25547



AL - 10 x 14 - 43134
PL - 10 x 14 - 25557



FG - 14 x 20 - 69023
AL - 10 x 14 - 43116
PL - 10 x 14 - 25539



AL - 10 x 14 - 43474
PL - 10 x 14 - 25897
SS - 10 x 14 - 95687



SS - 10 x 7 - 59382



FG - 5 x 14 - 71463
SS - 5 x 14 - 84956



SS - 3 1/2 x 10 - 84949



FG - 10 x 14 - 69035
AL - 7 x 10 - 43127
AL - 10 x 14 - 43128
PL - 10 x 14 - 25551




AL - 10 x 14 - 43108




FG - 14 x 20 - 71432



AL - 7 x 10 - 43139



SS - 10 x 7 - 84878



SS - 3 1/2 x 10 - 84950



SS - 7 x 10 - 84937
SS - 10 x 14 - 84938



SS - 7 x 10 - 84827
SS - 10 x 14 - 84828



AL - 7 x 10 - 43083



FG - 10 x 14 - 71425



SS - 7 x 10 - 84847



SS - 7 x 10 - 84843

Safety Signs

www.BradyID.com

Safety Signs

Electric Exit Signs and Evacuation Maps



Floodlights provide up to two hours of light for a safer exit in a power outage



Provides safety lighting in times of emergency

Big Beam® Combination Lighting

- 20 gauge steel cabinet can be ceiling or surface mounted
- Sealed lead calcium battery automatically recharges.
- Signs come with both red and green lettering panels to meet local codes.
- Dual voltage transformer for 120/277 VAC operation.
- UL listed.

Cat. No.	Description	Size (WxHxD)	Price
80139	Exit Sign with 8 watt sealed beam	25½"x13"x5"	\$262.63
80140	Exit Sign with 6 watt rectangular HIT lamps	12½"x13"x5"	\$234.30

Perimeter L.E.D. Exit Signs


- An economical alternative to traditional, incandescent or fluorescent exit signs.
- Listed to UL 924 and in compliance with OSHA, NEC® and NFP standards.
- Signs come with a 90-minute nickel cadmium battery back-up assembly for power failure.
- Standard input voltages are 120 or 277AC.
- Sign measures 12¼"W x 7½"H x 2½"D.

Catalog #	Description	Price
56905	Black Housing/Red Lens	\$251.08
56907	White Housing/Red Lens	\$251.08

Big Beam® Emergency Lighting

- Rectangular lights are 6 watt HIT lamps which last a minimum of 1½ hours in a power outage.
- UL listed.
- Dual voltage transformer for 120/277 VAC operation.
- Automatic recharger for the battery – no need for maintenance.

Catalog #	Description	Price
80141	Emergency light with rectangular lamps	\$156.10



Emergency Evacuation Frames

- Holders display your custom evacuation maps
- Clear acrylic frames hold your custom maps and allow you to easily change them when updates are needed

"Emergency Evacuation" Frame

Catalog #	Size (W x H)	Material	Price
102857	17½" X 15"	Luminous	\$111.15

"Evacuation Map" Frame

Catalog #	Size (W x H)	Material	Price
102852	17½" X 15"	Standard	\$88.47
102851	11½" X 11"	Luminous	\$99.81
102853	17½" X 15"	Luminous	\$111.15



Evacuation/Map Display/Holder

- Easy-to-see acrylic board
- Quickly shows viewers the best evacuation route from their work area
- Display size: 15" H x 11" W

Catalog #	Size	Price
45381	15"H X 11" W	\$49.97



Evacuation Plan Insert Holder

- Simply print and insert your evacuation map
- 17-1/2"w x 13-1/2"h frame holds standard 17" x 11" insert
- Non-glare, scratch-resistant finish
- Vivid red border with raised white lettering
- 2 adhesive mounting strips on back for easy installation

Catalog #	Size	Price
102849	17½" X 13½"	\$113.14

Exit & Directional Signs



OSHA Requirements

Not an Exit 1910.37(Q)

Any door, passage, or stairway that is not an exit or a way to get to an exit, but looks as though it could be an exit must be marked with a sign reading "NOT AN EXIT," or must be identified by a sign telling what it is, such as "to basement," "storeroom," "linen closet," or whatever it may be.

Evacuation Route 1910.38(a)(2), 1910.120(1)(2)(vi) (Informational marking)

Elements of an emergency response plan. The employer shall develop an emergency response plan for emergencies which shall address, as minimum, the following:...(vi) Evacuation routes and procedures.

Exit 1910.37(q)(1),(3),(4),(6),(8)

Exits shall be marked by a readily visible sign. They must be of such size, color and design as to be readily visible, contrasting with the colors and decorations around them. A sign reading "EXIT," with an arrow showing the directions, must be placed in every location where the direction of travel to get to the nearest exit is not immediately obvious.



FG - 7 x 10 - 47040*
 FG - 10 x 14 - 47288
 AL - 7 x 10 - 41053*
 AL - 10 x 14 - 41054
 PL - 7 x 10 - 22489*
 PL - 10 x 14 - 22490
 SS - 7 x 10 - 84673*
 SS - 10 x 14 - 84674



PL - 10 x 14 - 22492



FG - 10 x 14 - 70949
 AL - 7 x 10 - 41052*
 PL - 7 x 10 - 22488*
 SS - 7 x 10 - 84671*



(Reflective)
 B-997 - 7 x 10 - 95142*



PL - 7 x 10 - 22499*
 PL - 10 x 14 - 22500
 SS - 7 x 10 - 84685*



AL - 7 x 10 - 41065*
 AL - 10 x 14 - 41066
 FG - 7 x 10 - 71015*
 FG - 10 x 14 - 71016
 PL - 7 x 10 - 22501*
 PL - 10 x 14 - 22502
 SS - 10 x 14 - 84688
 SS - 7 x 10 - 84687*



AL - 10 x 14 - 43339
 PL - 10 x 14 - 25762
 SS - 10 x 14 - 84618




AL - 10 x 14 - 41046
 FG - 10 x 14 - 69199
 PL - 7 x 10 - 22481*
 PL - 10 x 14 - 22482
 SS - 7 x 10 - 84663*



PL - 7 x 10 - 22483*
 PL - 10 x 14 - 22484
 SS - 3 12 x 10 - 89156*
 SS - 7 x 10 - 84665*
 SS - 10 x 14 - 84666



FG - 7 x 7 - 76870
 AL - 7 x 10 - 41062
 PL - 7 x 10 - 22498
 SS - 7 x 7 - 84684



FG - 7 x 14 - 47035*
 AL - 10 x 14 - 41022
 PL - 7 x 10 - 22457*
 PL - 10 x 14 - 22458
 SS - 10 x 14 - 84632



FG - 7 x 14 - 47034*
 FG - 10 x 14 - 76067
 AL - 10 x 14 - 41020
 PL - 7 x 10 - 22455*
 PL - 10 x 14 - 22456
 SS - 10 x 14 - 84630



FG - 5 x 14 - 70915
 AL - 7 x 10 - 41044
 PL - 7 x 10 - 22480



SS - 5 x 14 - 84662



PL - 7 x 10 - 25764



Frameless Exit Sign - \$88.14

Red Exit 8.25 x 15.25 87807B
 Green Exit 8.25 x 15.25 87808B



45379 - \$34.73

High Visibility Exit Sign

- Made of polystyrene (B-493)
- V-shaped 45° angle
- 12"H x 18"W x 8"D

*Does not comply with 1910.37 character height requirements.

Sign materials and pricing can be found on page 23.

Safety Signs

www.BradyID.com

Safety Signs

BradyGlo™ Glow-in-the-Dark Exit & Directional Signs

BradyGlo™ Photoluminescent Signs

BradyGlo™ Photoluminescent Signs is a full line of photoluminescent signs and photoluminescent exit signs to help meet your egress needs.

B-324 Photoluminescent Self-Stick Polyester and B-347 Photoluminescent Plastic are electricity-free, and they do not need batteries or wiring. Brady BradyGlo™ Signs are ideal for green building and can help builders earn points to a variety of LEED credits.

These photoluminescent signs are a perfect option for exit signage where electrical power failure might be a possibility. They are 100% reliable, and ensure a safe, well-lit exit during evacuation.



B-324 - 7 x 10 - 73509*
B-324 - 10 x 14 - 73510
B-347 - 7 x 10 - 80281*
B-347 - 10 x 14 - 80282



B-324 - 7 x 10 - 80215*
B-324 - 10 x 14 - 73513
B-347 - 7 x 10 - 80283*
B-347 - 10 x 14 - 80284



B-324 - 7 x 10 - 73545*
B-324 - 10 x 14 - 80250
B-347 - 7 x 10 - 85484*
B-347 - 10 x 14 - 85523



B-324 - 7 x 10 - 90105*
B-324 - 10 x 14 - 90619
B-347 - 7 x 10 - 90947*
B-347 - 10 x 14 - 90631



B-324 - 7 x 10 - 73542*
B-324 - 10 x 14 - 80247
B-347 - 7 x 10 - 85480*
B-347 - 10 x 14 - 85481



B-324 - 10 x 14 - 80249
B-347 - 7 x 10 - 85482*
B-347 - 10 x 14 - 85483



B-324 - 7 x 10 - 90106
B-324 - 10 x 14 - 90620
B-347 - 7 x 10 - 90948
B-347 - 10 x 14 - 90632



B-324 - 10 x 14 - 90623
B-347 - 10 x 14 - 90635



B-324 - 10 x 14 - 90622
B-347 - 10 x 14 - 90634



B-324 - 10 x 14 - 90494
B-327 - 10 x 14 - 90495



B-324 - 7 x 10 - 90102*
B-324 - 10 x 14 - 90616
B-347 - 7 x 10 - 90944*
B-347 - 10 x 14 - 90628




B-324 - 7 x 10 - 80213*
B-324 - 10 x 14 - 80214
B-347 - 7 x 10 - 80279
B-347 - 10 x 14 - 80280



B-324 - 10 x 14 - 80255




B-324 - 10 x 14 - 80261
B-347 - 10 x 14 - 80028




B-324 - 5 x 14 - 80245



B-324 - 5 x 14 - 90592
B-347 - 5 x 14 - 90920



B-324 - 12 x 10 - 80207
B-324 - 5 x 14 - 80208
B-347 - 3 1/2 x 10 - 80273
B-347 - 5 x 14 - 80274



B-324 - 3 1/2 x 10 - 80201
B-347 - 3 1/2 x 10 - 80267
B-347 - 5 x 14 - 80268



B-324 - 14 x 10 - 80161
B-347 - 14 x 10 - 80292




B-324 - 14 x 10 - 78260
B-347 - 14 x 10 - 80173




B-324 - 14 x 10 - 80160
B-347 - 14 x 10 - 85463



B-324 - 10 x 7 - 90550
B-324 - 14 x 10 - 90183
B-347 - 10 x 7 - 90714



B-324 - 3 1/2 x 10 - 80209
B-324 - 5 x 14 - 80210
B-347 - 3 1/2 x 10 - 80275
B-347 - 5 x 14 - 80276



B-324 - 3 1/2 x 10 - 80211
B-324 - 5 x 14 - 80212
B-347 - 3 1/2 x 10 - 80277
B-347 - 5 x 14 - 80278



B-324 - 10 x 7 - 80217
B-324 - 14 x 10 - 80218
B-347 - 10 x 7 - 80285
B-347 - 14 x 10 - 80286




B-324 - 10 x 7 - 80219
B-324 - 14 x 10 - 80220
B-347 - 10 x 7 - 80287
B-347 - 14 x 10 - 80288




B-324 - 10 x 7 - 80221*
B-324 - 14 x 10 - 80222
B-347 - 10 x 7 - 80289*
B-347 - 14 x 10 - 80290



B-347 - 14 x 10 - 90777



B-324 - 3 1/2 x 10 - 80262
B-347 - 3 1/2 x 10 - 80029



B-324 - 3 1/2 x 10 - 80264
B-347 - 3 1/2 x 10 - 80040



B-347 - 14 x 5 - 80460



B-324 - 14 x 5 - 80223
B-347 - 14 x 5 - 80291



B-324 - 10 x 7 - 90155*
B-324 - 14 x 10 - 90157
B-347 - 10 x 7 - 90686*
B-347 - 14 x 10 - 90748



B-324 - 10 x 7 - 90156
B-324 - 14 x 10 - 90518
B-347 - 10 x 7 - 90687
B-347 - 14 x 10 - 90749



B-324 - 10 x 7 - 90158
B-324 - 14 x 10 - 90520
B-347 - 14 x 10 - 90751



B-324 - 10 x 7 - 90159*
B-324 - 14 x 10 - 90521
B-347 - 10 x 7 - 90690*
B-347 - 14 x 10 - 90752



B-324 - 10 x 7 - 90160*
B-324 - 14 x 10 - 90522
B-347 - 10 x 7 - 90691*
B-347 - 14 x 10 - 90753



V1SWG4G - V Style - \$23.70
6"H x 9"W x 4"D

IBC/IFC Compliant BradyGlo™ Directional Exit Signs

- Doors opening to corridors where such corridors act as required exit passageways connecting two vertical exits
- Doors serving as horizontal exits or stairwell exits
- Transfer levels and wherever egress direction is not clear
- Self-Sticking (B-984), Polystyrene (B-985) and Aluminum (B-986)



B-986 - 7 x 15 - 114687 - \$47.00
B-985 - 7 x 15 - 114686 - \$37.00
B-984 - 7 x 15 - 114685 - \$25.00



B-986 - 7 x 15 - 114675 - \$47.00
B-985 - 7 x 15 - 114674 - \$37.00
B-984 - 7 x 15 - 114673 - \$25.00



B-986 - 7 x 15 - 114690 - \$47.00
B-985 - 7 x 15 - 114689 - \$37.00
B-984 - 7 x 15 - 114688 - \$25.00



B-986 - 7 x 15 - 114678 - \$47.00
B-985 - 7 x 15 - 114677 - \$37.00
B-984 - 7 x 15 - 114676 - \$25.00



B-986 - 7 x 15 - 114693 - \$47.00
B-985 - 7 x 15 - 114692 - \$37.00
B-984 - 7 x 15 - 114691 - \$25.00



B-986 - 7 x 15 - 114681 - \$47.00
B-985 - 7 x 15 - 114680 - \$37.00
B-984 - 7 x 15 - 114679 - \$25.00



B-986 - 14 x 10 - 114639 - \$62.00
B-985 - 14 x 10 - 114638 - \$52.00
B-984 - 14 x 10 - 114637 - \$40.00



B-986 - 14 x 10 - 114642 - \$62.00
B-985 - 14 x 10 - 114641 - \$52.00
B-984 - 14 x 10 - 114640 - \$40.00



B-986 - 7 x 21 - 114660 - \$52.00
B-985 - 7 x 21 - 114659 - \$42.00
B-984 - 7 x 21 - 114658 - \$30.00



B-986 - 7 x 21 - 114651 - \$52.00
B-985 - 7 x 21 - 114650 - \$42.00
B-984 - 7 x 21 - 114649 - \$30.00



B-986 - 7 x 21 - 114663 - \$52.00
B-985 - 7 x 21 - 114662 - \$42.00
B-984 - 7 x 21 - 114661 - \$30.00



B-986 - 7 x 21 - 114654 - \$52.00
B-985 - 7 x 21 - 114653 - \$42.00
B-984 - 7 x 21 - 114652 - \$30.00



B-986 - 7 x 21 - 114666 - \$52.00
B-985 - 7 x 21 - 114665 - \$42.00
B-984 - 7 x 21 - 114664 - \$30.00



B-986 - 7 x 21 - 114657 - \$52.00
B-985 - 7 x 21 - 114656 - \$42.00
B-984 - 7 x 21 - 114655 - \$30.00



B-986 - 10 x 22 - 114648 - \$78.00
B-985 - 10 x 22 - 114647 - \$68.00
B-984 - 10 x 22 - 114646 - \$56.00



B-986 - 10 x 22 - 114643 - \$78.00
B-985 - 10 x 22 - 114644 - \$68.00
B-984 - 10 x 22 - 114645 - \$56.00

IBC/IFC, NYC Compliant BradyGlo™ Exit Sign

- Compliant to NFPA Life Safety Code 101 and 2009 IBC and current building codes
- Energy efficient, non-electric, non toxic, non-radioactive and may qualify for LEED credits
- 50–75 ft visibility, 100% reliable and virtually maintenance free
- 3 configurations which can be attached on a surface, ceiling or flag mounted



Framed BradyGlo™ Exit Signs



Frameless BradyGlo™ Exit Signs



BradyGlo™ Kick Plate Exit Sign

Framed BradyGlo™ Exit Signs

Color	Single Face Wall Mount \$163.08	Single Face w/Bracket \$201.59	Double Face w/brack \$319.19	Mounting Bracket Only \$50.40
Black	37851B	38097B	38098B	38099B
Red	90885B	90839B	90840B	90886B
Green	90887B	90841B	90842B	90888B
White	80753B	80754B	80755B	80756B
Silver	112653B	112654B	112655B	112656B

Frameless BradyGlo™ Exit Signs

Catalog #	Description	Price
87807B	Frameless Red Exit Sign	\$88.14
87808B	Frameless Green Exit Sign	\$88.14

BradyGlo™ Kick Plate Exit Signs

Catalog #	Description	Price
113063B	Kick Plate Exit Sign	\$229.00

IBC/IFC Compliant BradyGlo™ Door Handle Markers



Plastic Push Bar Door Marker



Plastic Door Handle Marker - Vertical



Plastic Door Handle Marker - Horizontal

Description	Size H x W	Catalog #	Price
Plastic Push Bar Door Marker - Push	2" x 30"	114912	\$30.95
Plastic Push Bar Door Marke - Blank	2" x 30"	114913	\$30.95
Plastic Push Bar Door Marke - Push	1.5" x 18"	114914	\$15.95
Plastic Push Bar Door Marke - Blank	1.5" x 18"	114915	\$15.95
B-984 Self-Sticking Adhesive	4.125" x 4.125"	114697	\$15.25

Description	Size H x W	Catalog #	Price
Plastic Door Handle Marker - Vertical - Exit	7" x 10"	114917	\$19.95
Plastic Door Handle Marker - Vertical - Blank	7" x 10"	114918	\$19.95
Plastic Door Handle Marker - Horizontal - Left - Exit	7" x 10"	114919	\$19.95
Plastic Door Handle Marker - Horizontal - Right - Exit	7" x 10"	114921	\$19.95

Sign materials and pricing can be found on page 23.

Safety Signs

www.BradyID.com

Safety Signs

Fire Safety



OSHA Requirements

Flammable: Keep Fire Away 1910.106(d)(3)(ii)

Storage cabinets in which you keep flammable liquids, such as gasoline, must be labeled in conspicuous lettering, "Flammable – Keep Fire Away."

Fire Extinguisher Marking 1910.157(c)(1)

If you are using portable fire extinguishers, you must mount, locate and identify them so that they are readily accessible to employees.

Fire Hose 1910.158(c)(1)

Where reels or cabinets are provided to contain fire hose, the employer must be sure that they are conspicuously identified and used only for fire equipment.



SS - 7 x 10 - 90372



AL - 10" x 14" - 95504
AL - 14 x 20 - 95505



SS - 7 x 10 - 85253



FG - 10 x 14 - 73434
PL - 7 x 10 - 25729
SS - 10 x 14 - 85278



PL - 10 x 14 - 25914



FG - 7 x 7 - 69243
PL - 7 x 10 - 25169
SS - 7 x 7 - 88504



AL - 10 x 14 - 41253



AL - 10 x 14 - 43258



AL - 7 x 10 - 43290
PL - 7 x 10 - 25713
SS - 5 x 14 - 85255



PL - 7 x 10 - 25722
SS - 5 x 14 - 85269



B-324 - 5 x 14 - 80242



B-324 - 5 x 14 - 80202



FG - 5 x 14 - 71649
SS - 3 1/2 x 10 - 85256



SS - 3 1/2 x 14 - 85259



FG - 14 x 10 - 69074
AL - 14 x 10 - 43294
PL - 14 x 10 - 25717
SS - 14 x 10 - 86091
B-324 - 14 x 10 - 80162



AL - 14 x 10 - 43285
PL - 14 x 10 - 25708
SS - 14 x 10 - 86090




SS - 10 x 14 - 90383



SS - 14 x 5 - 85270



FG - 14 x 3 1/2 - 47039
FG - 24 x 4 - 71655
AL - 10 x 7 - 43295
PL - 10 x 7 - 25718
SS - 14 x 3 1/2 - 85261
SS - 14 x 5 - 90367
B324 - 14 x 5 - 80241



SS - 14 x 28 - 90369

When wrapped around columns the word "Fire Extinguisher" is repeated 4 times. Or can be cut into four 14" x 7" single signs.




Fire/Exit Sign 6 Pack

PL - 10" x 18" - 51556 - \$75.06
SS - 10" x 18" - 51555 - \$62.30


High Visibility Fire Safety

High Visibility Fire Safety Signs

Brady's High Visibility signs are designed to be seen from all access points in your facility. They are available in both L-Style 90° and V-Style 45° angles and are used to clearly mark fire safety equipment for quick and easy access in an emergency situation



L-Style 90° Angle
(Legend appears on both sides)



V-Style 45° Angle
(Legend repeated on outward facing side)



B-493 - 45368 - \$21.84
5½"H x 10"W x 4"D



B-493 - 45366 - \$21.84
5½"H x 10"W x 4"D



B-493 - 45365 - \$21.84
5½"H x 10"W x 4"D



V1FE15A - V Style - \$14.95
6"H x 9"W x 4"D



V1FL15A - V Style - \$14.95
6"H x 9"W x 4"D



B-493 - 80703 - \$24.98
8"H x 14½"W x 6"D



LOFE15A - L-style - \$16.20
8" x 8"

V1FEG1G - V Style - \$23.70
6"H x 9"W x 4"D



High Visibility Fire Extinguisher Sign

- Made of B-450 Rigid Polyethylene

L Style 90° angle

Cat. No.	Legend	Size W x H	Style	Price
45422	Exit	9 x 12	L- Style	\$15.55
70998	Fire Extinguisher	9 x 12	L- Style	\$15.55
96908	Fire Extinguisher	12 x 18	V- Style	\$22.11



"V - Style"



"L - Style"

Tall Fire Extinguisher Acrylic Signs

- Wall mounting package included

Cat. No.	Size W x H	Style	Price
SP184L	4½"W x 18"H x 3½"D	L- Style	\$18.70
SP818V	8½"W x 18"H	V- Style	\$23.69



L-Style High Visibility Signs - legend appears on both sides



V-Style High Visibility Sign

BradyGlo™ High Visibility Fire Safety Signs

- For safety instructions and egress during power outages and emergency situations
- Exceed ASTM E 2072-00 standard specifications for phospholuminescent safety markings
- Available in L-Style (90° angle) or V-Style (45° angle)
- Constructed of B-347 BradyGlo™ Photoluminescent Plastic

L Style, Material: B-347 90° angle

Cat. No.	Legend	Size W x H	Color Legend/Bkgrd.	Price
94044	Fire Extinguisher	9 x 12	white/red	\$38.57

V Style, Material: B-347 45° angle

Cat. No.	Legend	Size W X H	Color Legend/Bkgrd.	Price
94008	Fire Extinguisher	9 X 12	white/red	\$66.91
94022	Exit	9 X 12	white/red	\$66.91
94027	Fire Alarm	9 X 12	white/red	\$66.91
94029	Fire Hose	9 X 12	white/red	\$66.91



2-Way View Fire Safety Signs

- Distinctly mark equipment with these two-sided signs
- Made from BradyGlo™ Plastic (B-347) or Plastic (B-401)

L-Style

Cat. No.	Legend	Material	Size	Color	Price
50688	Fire Alarm	B-347	4 x 12	Green on Red	\$21.71
50692	Fire Extinguisher	B-347	4 x 12	Green on Red	\$21.71
50693	Fire Extinguisher	B-401	4 x 18	White on Red	\$28.57
50694	Fire Extinguisher	B-347	4 x 18	Green on Red	\$37.70
50696	Fire Hose	B-347	4 x 12	Green on Red	\$22.80
50698	Fire Hose	B-347	4 x 18	Green on Red	\$37.70



3-Way View Fire Safety Signs

- Angular signs point out emergency equipment and exits
- Made from BradyGlo™ Plastic (B-347)

V-Style

Cat. No.	Legend	Size	Color	Price
50784	Fire Hose	7½ x 18	Red on Green	\$69.83
50786	Fire Extinguisher	7½ x 18	Red on Green	\$69.83
50778	Fire Equipment	7½ x 18	Red on Green	\$69.83

Safety Signs

www.BradyID.com

Safety Signs

First Aid Signs



OSHA Requirements

First Aid 1910.252(f)(13), 1910.151(b) (Informational marking)

First aid supplies...shall be readily available.

Emergency Eyewash and Shower 1910.151(c) (Informational Marking)

Suitable facilities for quick drenching or flushing of the eyes and body must be provided in the work area for emergency use if workers' eyes or bodies are exposed to injurious corrosive materials. Appendix A (non-mandatory appendix) to 1910.1450, the National Research Council Recommendations Concerning Chemical Hygiene in Laboratories, recommends that location signs for safety showers, eyewash stations and other safety and first aid equipment be posted.

Respirators 1910.134(f)(5)(i)

Respirators placed at stations and work areas for emergency use should be quickly accessible at all times and should be stored in compartments built for this purpose. The compartments should be clearly marked.



FG - 10 x 14 - 72700
PL - 10 x 14 - 22662
SS - 10 x 14 - 85350



FG - 7 x 10 - 72722
AL - 7 x 10 - 41229
PL - 7 x 10 - 22665
SS - 7 x 10 - 85354
SS - 10 x 14 - 85355



AL - 10 x 14 - 43481
PL - 10 x 14 - 25904



PL - 10 x 14 - 26582



PL - 7 x 10 - 22642



PL - 7 x 10 - 25167
SS - 7 x 7 - 88502



PL - 7 x 10 - 22650
SS - 7 x 10 - 85331



FG - 10 x 14 - 72883
PL - 7 x 10 - 22686
SS - 10 x 14 - 85378




FG - 14 x 20 - 73493
AL - 10 x 14 - 41219
PL - 10 x 14 - 22655



FG - 14 x 10 - 75963
PL - 14 x 10 - 22647




FG - 14 x 10 - 47044
PL - 14 x 10 - 22645
SS - 10 x 7 - 85323



PL - 7 x 10 - 22671
SS - 3 1/2 x 10 - 85361



FG - 7 x 17 - 69232



SS - 3 1/2 x 10 - 85359
B-324 - 3 1/2 x 10 - 73538

High Visibility First Aid Signs



V1FA03A - V Style
6"H x 9"W x 4"D



V1AE01A - V Style
6"H x 9"W x 4"D



V1EW03A - V Style
6"H x 9"W x 4"D




B-493 - 45370 - \$21.84
5 1/2"H x 10"W x 4"D




B-493 - 45363 - \$21.84
5 1/2"H x 10"W x 4"D

B-493 - 80704 - \$34.74
12"H x 18"W x 8"D



L-Style
90° Angle



V-Style
45° Angle

Catalog Number	Legend	Material	Style	Size H x W	Color Legend/Bkgrd.	Price
49041	Eye Wash	B-450	L-Style	12 x 9	green on white	\$15.55
49044	Eye Wash	B-450	V-Style	12 x 18	green on white	\$22.11

Sign materials and pricing can be found on page 23.

Floor Signs

! OSHA Requirements

Phosphorescent Floor Signs address section 4.2.1 Floor Mounted Markings

The ASTM guide for recommended uses of Photoluminescent safety markings describes recommended uses and information on installation of photoluminescent safety markings to supplement emergency lighting.

Floor Safety Signs

- 17" Diameter
- Vinyl Film with Clear, Matte Anti-Slip Overlaminated
- Price \$34.84



ToughStripe™ Anti-Slip Floor Signs

ToughStripe™ floor signs are made with Brady's new B-534 polyester. They are specifically designed to alert workers of potential dangers and enforce protective equipment requirements.

- Exceeds safety standards for clean, dry non-slip surfaces per ANSI A1264.2-2006 and OSHA 1910.22
- Service temperature range of 0°F – 129°F
- 3 mil thickness. 14" x 18" Square or 17" Diameter Circle
- Price \$38.70



Sign materials and pricing can be found on page 23.

Safety Signs


www.BradyID.com

Safety Signs


Funny Signs



PL - 7 x 10 - 38067



PL - 7 x 10 - 38073



PL - 7 x 10 - 38071



PL - 10x7 - 38076

Gate Signs



95444



95448

Handicapped Signs



FG - 6 x 6 - 94336
B-959 - 12 x 12 - 94174



FG - 9 x 9 - 91332
FG - 12 x 12 - 91333
B-959 - 12 x 12 - 91358



B-959 - 12 x 18 - 91357



FG - 18 x 12 - 91336
B-959 - 18 x 12 - 91362



FG - 18 x 12 - 91334
B-959 - 18 x 12 - 91360



B-959 - 18 x 12 - 91356

Handicap Parking Requirements

Total Spaces in Parking Lot	Min. Number of Handicap Spaces
1 to 25	1
26 to 50	2
51 to 75	3
76 to 100	4
101 to 150	5
151 to 200	6
201 to 300	7
301 to 400	8
401 to 500	9
501 to 1,000	2% of total
More than 1,000	20 plus 1 for every 100 over 1,000



\$250 Fine:
B-959 - 6 x 12 - 80049
\$350 Fine:
B-959 - 6 x 12 - 112500



B-959 - 6 x 12 - 91326



B-959 - 6 x 12 - 91387



B-959 - 18 x 12 - 91363



B-959 - 18 x 12 - 80110



B-959 - 18 x 12 - 90018



B-959 - 18 x 12 - 94175



B-959 - 18 x 12 - 91352



B-959 - 18 x 12 - 91351

NEW! Hospital Signs

Universal Health Care Symbols were developed to represent all the hospital functions that are universal to most health care buildings.

Brady has created these signs to improve the health care environment by creating communication tools that help any visitor navigate through any hospital.

- Accommodate multiculturalism by using symbols
- May be used to create a new way finding solution, or may compliment an already existing system
- Represent the most common activities to health care facilities and environments
- Available in aluminum, plastic and self-sticking.
- Customizable by size, text and color



B-302 - 4x4 - 142616
B-302 - 8x8 - 142575



B-302 - 4x4 - 142629
B-302 - 8x8 - 142575



B-302 - 4x4 - 142643
B-302 - 8x8 - 142589



B-302 - 4x4 - 142633
B-302 - 8x8 - 142579



B-555 - 10x7 - 142433
B-401 - 10x7 - 142487
B-302 - 10x7 - 142541



B-555 - 10x7 - 142406
B-401 - 10x7 - 142460
B-302 - 10x7 - 142514



B-555 - 10x7 - 142439
B-401 - 10x7 - 142493
B-302 - 10x7 - 142547



B-555 - 10x7 - 142395
B-401 - 10x7 - 142449
B-302 - 10x7 - 142503

View all 160 Hospital Signs at www.BradyID.com.

Sign materials and pricing can be found on page 23.

Machine & Operational



AL - 10 x 14 - 42535
FG - 10 x 14 - 47022
PL - 10 x 14 - 23012



PL - 7 x 10 - 23009



PL - 7 x 10 - 22945



SS - 3 1/2 x 5 - 88172



FG - 10 x 14 - 74187
AL - 10 x 14 - 42507
PL - 10 x 14 - 22984
SS - 7 x 10 - 88101
SS - 10 x 14 - 88102



FG - 10 x 14 - 74609
AL - 7 x 10 - 42508
AL - 10 x 14 - 42509
PL - 10 x 14 - 22986
SS - 3 1/2 x 5 - 87788
SS - 10 x 14 - 88108



AL - 10 x 14 - 42531



AL - 10 x 14 - 42501
PL - 10 x 14 - 22978



FG - 10 x 14 - 69541
SS - 7 x 10 - 88189



SS - 7 x 10 - 85985



AL - 10 x 14 - 43490
PL - 10 x 14 - 25913



FG - 7 x 10 - 47160
FG - 10 x 14 - 47192
AL - 7 x 10 - 42562
AL - 10 x 14 - 42563
PL - 7 x 10 - 23039
PL - 10 x 14 - 23040
SS - 3 1/2 x 5 - 87792
SS - 7 x 10 - 88185
SS - 10 x 14 - 88186



FG - 10 x 14 - 74264
AL - 10 x 14 - 42525
PL - 10 x 14 - 23002
SS - 10 x 14 - 88132



AL - 7 x 10 - 42556



AL - 10 x 14 - 60509



SS - 10 x 14 - 60575



SS - 7 x 10 - 88183



FG - 7 x 17 - 69028



FG - 10 x 14 - 74132
AL - 10 x 14 - 42489
PL - 10 x 14 - 22966
SS - 10 x 14 - 85972



SS - 7 x 10 - 88327



FG - 20 x 14 - 71118



AL - 14 x 10 - 42455
PL - 14 x 10 - 22932
SS - 5 x 3 1/2 - 85890
SS - 7 x 5 - 85891
SS - 14 x 10 - 85893



AL - 14 x 10 - 42433
FG - 14 x 10 - 65570
PL - 14 x 10 - 22910
vSS - 14 x 10 - 85849



45367 - V Style - \$21.84
5 1/2" H x 10" W x 4" D



FG - 10 x 14 - 74270
AL - 7 x 10 - 42440
AL - 10 x 14 - 42441
PL - 7 x 10 - 22917
PL - 10 x 14 - 22918
SS - 7 x 10 - 85858
SS - 10 x 14 - 85859



AL - 10 x 14 - 43500



PL - 10 x 14 - 25906
AL - 10 x 14 - 43483



FG - 14 x 20 - 74442



AL - 7 x 10 - 42442
SS - 7 x 10 - 85860



V2SS24A - V Style - \$18.69
8" H x 15" W x 6" D



FG - 10 x 14 - 70470
AL - 10 x 14 - 42447
PL - 10 x 14 - 22924



AL - 10 x 14 - 42387
PL - 10 x 14 - 22864



PL - 7 x 10 - 22879
SS - 3 1/2 x 5 - 87791
SS - 7 x 10 - 85797



PL - 7 x 10 - 22875



AL - 7 x 10 - 42621
SS - 7 x 10 - 88288



SS - 2 1/4 x 4 1/2 - 88304



FG - 7 x 17 - 70577

Safety Signs

www.BradyID.com

Safety Signs

Maintenance



AL - 10 x 14 - 41337
PL - 10 x 14 - 22773
SS - 10 x 14 - 85599



FG - 10 x 14 - 72975



FG - 7 x 10 - 72800
PL - 7 x 10 - 22842
SS - 7 x 10 - 85720



FG - 18 x 12 - 73439



PL - 10 x 14 - 25752



AL - 10 x 14 - 43176



PL - 10 x 14 - 22801



PL - 10 x 14 - 22803



PL - 10 x 14 - 95500



PL - 10 x 14 - 22844
SS - 10 x 14 - 85724



FG - 10 x 14 - 69444



PL - 10 x 14 - 95503



OSHA Requirements

Appendix A to 1910.1450

Appendix A (non-mandatory appendix) to 1910.1450 recommends that signs designating areas where food and beverages can be consumed and stored be posted.

Do Not Enter Lunchroom - 29 CFR 1926.62(i)(4)

The employer shall assure that employees do not enter lunchroom facilities or eating areas with protective work clothing or equipment unless surface lead dust has been removed by vacuuming, downdraft booth, or other cleaning method that limits dispersion of lead dust.

Housekeeping, Keeping the Aisles Clean - 29 CFR 1910.22(a)(1)-(2)

Every workplace, including aisles, storerooms and service rooms must be kept clean and orderly, and in a sanitary condition. Work room floors should be kept dry, with adequate drainage provided.

No Food or Drink Beyond This Point 1910.141(g)

No employee shall be allowed to consume food or beverages in an area exposed to toxic material or in a toilet room.

Load Rating Plate 1910.22(d)

In every building or structure used for mercantile, business, industrial or storage purposes, the loads approved by the building official shall be marked on plates of approved design and shall be affixed by the owner of the building, or his authorized agent, in a conspicuous place in each space to which they relate.

NEW!

Create Custom Safety Signs Online

Create made-to-order OSHA and ANSI Safety Signs for your facility with this easy-to-use application. Select your header, pictogram, size, wording and more.

- 11 Headers in English & Spanish
- 9 Categories of Pictograms
- 4 Sign Material Choices

Try the Custom Design Tool at www.BradyID.com!

Easy as 1, 2, 3!

- 1) Select your category
- 2) Customize your product
- 3) Add to your shopping cart



Create custom products in minutes!

Ships in 24-48 hours!

Also available for Traffic & Parking Signs!

No Smoking

OSHA Requirements

No Smoking 1910.106(e)(6)

Adequate precautions shall be taken to prevent the ignition of flammable vapors. Sources of ignition include but are not limited to open flames; lightning; smoking...

Battery Charging Area 1910.178(g)

Battery charging installations shall be located in areas designated for that purpose.

1910.103(b)(1)

Hydrogen gas is generated in battery charging areas. Smoking shall be prohibited in the charging area.

No Smoking, No Open Flames, No Water Reactive Materials 1910.106(d)(7)

Open flames and smoking shall not be permitted in flammable or combustible liquid storage areas. Water reactive materials may not be stored in the same room with flammable or combustible liquids



FG - 10 x 7 - 141924
AL - 10 x 7 - 141926
PL - 10 x 7 - 141928
SS - 10 x 7 - 141925
B-946 - 10 x 7 - 141928



FG - 10 x 7 - 141959
AL - 10 x 7 - 141961
PL - 10 x 7 - 141963
SS - 10 x 7 - 141960
B-946 - 10 x 7 - 141962



New Jersey State Smoking Ban


FG - 10 x 7 - 110977
FG - 14 x 10 - 110976
AL - 10 x 7 - 110973
AL - 14 x 10 - 110972
PL - 10 x 7 - 110975
PL - 14 x 10 - 110972
SS - 10 x 7 - 110978
SS - 14 x 10 - 110979



FG - 10 x 7 - 141939
AL - 10 x 7 - 141941
PL - 10 x 7 - 141943
SS - 10 x 7 - 141940
B-946 - 10 x 7 - 141942



AL - 10 x 14 - 42670



FG - 5 x 14 - 72040
AL - 7 x 10 - 42687
PL - 7 x 10 - 25110
SS - 5 x 14 - 88418



SS - 3 1/2 x 10 - 88421



FG - 10 x 14 - 72148
AL - 10 x 14 - 42712
PL - 10 x 14 - 25135
SS - 10 x 14 - 88452



FG - 10 x 14 - 47203
FG - 14 x 20 - 75670
AL - 10 x 14 - 42658
PL - 10 x 14 - 25081
SS - 7 x 10 - 88376
SS - 10 x 14 - 88377



FG - 7 x 10 - 47171
FG - 10 x 14 - 47010
AL - 10 x 14 - 42654
PL - 10 x 14 - 25077
SS - 7 x 10 - 88370
SS - 10 x 14 - 88371



FG - 10 x 7 - 72293
FG - 14 x 10 - 73486
FG - 20 x 14 - 72295
AL - 10 x 7 - 42696
AL - 14 x 10 - 42697
PL - 10 x 7 - 25119
PL - 14 x 10 - 25120
SS - 3 1/2 x 5 - 87795
SS - 10 x 7 - 88427
SS - 14 x 10 - 88428



AL - 10 x 14 - 43489



Use 2" numbers:
FG - 14 x 20 - 72255
Use 1" numbers:
SS - 7 x 10 - 88413



AL - 10 x 14 - 72397
PL - 10 x 14 - 72399
SS - 7 x 10 - 72355



Use 2" letters:
FG - 14 x 20 - 72155
Use 1" letters:
AL - 10 x 14 - 42714
PL - 10 x 14 - 25137
SS - 7 x 10 - 88453



FG - 10 x 14 - 72118
AL - 7 x 10 - 42659
AL - 10 x 14 - 42660
PL - 7 x 10 - 25082
PL - 10 x 14 - 25083
SS - 7 x 10 - 88378
SS - 10 x 14 - 88379



FG - 10 x 14 - 141944
FG - 14 x 20 - 141949
AL - 10 x 14 - 141946
AL - 14 x 20 - 141951
PL - 10 x 14 - 141948
PL - 14 x 20 - 141953
SS - 10 x 14 - 141945
SS - 14 x 20 - 141950
B-946 - 10 x 14 - 141947
B-946 - 14 x 20 - 141952



B-324 - 7 x 10 - 80248



FG - 10 x 14 - 72176
AL - 7 x 10 - 42721
PL - 7 x 10 - 25144
SS - 10 x 14 - 88468



Use 1" numbers:
AL - 10 x 14 - 42662
SS - 10 x 14 - 88381



FG - 10 x 14 - 141954
AL - 10 x 14 - 141956
PL - 10 x 14 - 141958
SS - 10 x 14 - 141955
B-946 - 10 x 14 - 141957



AL - 7 x 10 - 42692
AL - 10 x 14 - 42693
PL - 7 x 10 - 25115
PL - 10 x 14 - 25116
SS - 7 x 10 - 88423
SS - 10 x 14 - 88424



FG - 10 x 14 - 141929
FG - 14 x 20 - 141934
AL - 10 x 14 - 141931
AL - 14 x 20 - 141936
PL - 10 x 14 - 141933
PL - 14 x 20 - 141938
SS - 10 x 14 - 141930
SS - 14 x 20 - 141935
B-946 - 10 x 14 - 141932
B-946 - 14 x 20 - 141937



FG - 14 x 20 - 72091



FG - 10 x 14 - 46990
AL - 7 x 10 - 42685
PL - 7 x 10 - 25108
SS - 10 x 14 - 88412



FG - 10 x 14 - 72336
AL - 10 x 14 - 42725
PL - 10 x 14 - 25148
SS - 10 x 14 - 88472



FG - 7 x 10 - 72022
FG - 10 x 14 - 72024
AL - 10 x 14 - 42695
PL - 7 x 10 - 25117
PL - 10 x 14 - 25118
SS - 10 x 14 - 88426



FG - 10 x 14 - 141919
AL - 10 x 14 - 141921
PL - 10 x 14 - 141923
SS - 10 x 14 - 141920
B-946 - 10 x 14 - 141922



FG - 10 x 14 - 141964
FG - 14 x 20 - 141969
AL - 10 x 14 - 141966
AL - 14 x 20 - 141971
PL - 14 x 20 - 141973
PL - 10 x 14 - 141968
SS - 10 x 14 - 141965
SS - 14 x 20 - 141970
B-946 - 10 x 14 - 141967
B-946 - 14 x 20 - 141972

State Smoking Bans

Brady also offers other state specific No-Smoking signs. Visit www.bradyid.com and search by the state name.

Personal Protection Signs



OSHA Requirements

Ear Protection

Ear Protection Required 1910.145(c)(2)

Caution signs are to be posted to indicate a possible hazard against which proper precautions should be taken. Whenever an employee is exposed to sound levels exceeding the levels prescribed by OSHA, the employer must ensure that hearing protection is worn. This informational marking serves to remind employees that they have entered an area where hearing protection must be worn.

Eye Protection

Eye Protection Required 1910.145(c)(2)

Caution signs are to be posted to indicate a possible hazard against which proper precautions should be taken.

1910.242(b)

Compressed air may only be used for cleaning purposes when the pressure is reduced to less than 30 p.s.i. and then only when effective chip guarding and personal protective equipment is used.

Fall Protection

Accident Prevention 1910.145(c)(2)

Caution signs shall be used only to warn against potential hazards or to caution against unsafe practices. All employees shall be instructed that caution signs indicate a possible hazard against which proper precaution should be taken.

Ear Protection



FG - 10 x 14 - 73461
SS - 7 x 10 - 84796



FG - 10 x 14 - 70302
PL - 10 x 14 - 25463



FG - 14 x 10 - 105729



PL - 10 x 14 - 25891



FG - 10 x 14 - 47101
AL - 10 x 14 - 43042
PL - 10 x 14 - 25465
SS - 7 x 10 - 84784
SS - 10 x 14 - 84785



FG - 10 x 14 - 84815
AL - 10 x 14 - 43068
PL - 10 x 14 - 25491
SS - 10 x 14 - 47332



AL - 14 x 10 - 43034
PL - 14 x 10 - 25457



AL - 10 x 14 - 43471
PL - 10 x 14 - 25894



SS - 10 x 14 - 84775

Eye Protection



AL - 10 x 14 - 43469
PL - 10 x 14 - 25892



FG - 10 x 14 - 70339
PL - 10 x 14 - 22587



FG - 14 x 20 - 74630
AL - 7 x 10 - 41156
PL - 10 x 14 - 22593
SS - 7 x 10 - 84991



AL - 10 x 14 - 41193
PL - 10 x 14 - 22629



AL - 10 x 14 - 41159
PL - 7 x 10 - 22594
PL - 10 x 14 - 22595
SS - 7 x 10 - 84993
SS - 10 x 14 - 84994



FG - 10 x 14 - 69041



PL - 10 x 14 - 22615



FG - 10 x 14 - 47334
PL - 7 x 10 - 22626
SS - 7 x 10 - 85035
SS - 10 x 14 - 85036



AL - 10 x 14 - 43160
SS - 10 x 14 - 85056



FG - 7 x 10 - 70338
FG - 10 x 14 - 74479
PL - 10 x 14 - 25583

Fall Protection



FG - 10 x 14 - 74455
AL - 7 x 10 - 43187
AL - 10 x 14 - 43188
PL - 7 x 10 - 25610
PL - 10 x 14 - 25611
SS - 7 x 10 - 85097
SS - 10 x 14 - 85098



FG - 7 x 10 - 74299
PL - 10 x 14 - 25619



AL - 10 x 14 - 43198
PL - 7 x 10 - 25620



PL - 10 x 14 - 25607



FG - 7 x 17 - 69551



FG - 7 x 10 - 74680
PL - 7 x 10 - 25608
PL - 10 x 14 - 25609
SS - 7 x 10 - 85095



FG - 10 x 14 - 70528
PL - 10 x 14 - 25599
SS - 10 x 14 - 85086



AL - 10 x 14 - 43178
PL - 10 x 14 - 25601

Personal Protection Signs

Personal Protection Wear (PPE)



FG - 10 x 14 - 70475
AL - 10 x 14 - 42782
PL - 7 x 10 - 25204
PL - 10 x 14 - 25205
SS - 7 x 10 - 88571
SS - 10 x 14 - 88572



FG - 10 x 14 - 65039



AL - 10 x 14 - 43472
PL - 10 x 14 - 25895



FG - 10 x 14 - 74740
AL - 10 x 14 - 42784
PL - 10 x 14 - 25207
SS - 10 x 14 - 88584



PL - 10 x 14 - 25197



AL - 10 x 14 - 42778
PL - 10 x 14 - 25201



FG - 10 x 14 - 70358



PL - 10 x 14 - 25893



AL - 10 x 14 - 43476
PL - 10 x 14 - 25899



AL - 10 x 14 - 42794



PL - 10 x 14 - 60540



FG - 10 x 14 - 73474
PL - 7 x 10 - 25149
PL - 10 x 14 - 25150
SS - 7 x 10 - 88475



AL - 10 x 14 - 42822
PL - 10 x 14 - 25245



SS - 7 x 10 - 88643




SS - 7 x 10 - 88479



AL - 10 x 14 - 42792
PL - 10 x 14 - 25215



AL - 10 x 14 - 42923



Safety Stop Station

- Combines safety message and required safety equipment at one convenient location
- Constructed of durable red and clear acrylic
- Use indoors or outdoors
- Mount to a wall or use as a stand-alone sign
- Holds 12 pairs of glasses
- Station only; base and post sold separately

Catalog #	Size	Legend	Price
50914	36" x 18"	Stop Eye Protection Required Beyond This Point	\$281.73

Radiation And Laser Signs

OSHA Requirements

Radioactive Materials 1910.96(e)(5)
A sign or signs bearing the radiation caution symbol and the words: "Caution Radioactive Materials" must be posted.

High Radiation Area 1910.96(e)(3)(i)
Each high radiation area must be posted with a sign or signs bearing the radiation caution symbol and the words "High Radiation Area".



PL - 7 x 10 - 25278



FG - 7 x 10 - 74855
AL - 10 x 14 - 42862
PL - 7 x 10 - 25284
SS - 7 x 10 - 88748
SS - 10 x 14 - 88749



PL - 14 x 10 - 25277
SS - 14 x 10 - 88739



SS - 2 1/4 x 2 1/4 - 89112
SS - 3 1/2 x 10 - 88750



SS - 3 1/2 x 10 - 88752



SS - 7 x 10 - 88725



AL - 10 x 14 - 42865
PL - 10 x 14 - 25288
SS - 5 x 14 - 88762

Safety Signs

www.BradyID.com

Safety Signs

Recycle & Environment



SS - 7 x 10 - 86015



SS - 7 x 10 - 86009



B-946 - 1 x 2 1/4 - 76290
(9 per card)

Restrooms



FG - 4 x 12 - 70426



PL - 7 x 10 - 47670



PL - 7 x 10 - 47676



FG - 4 x 12 - 70593


Scoreboards



28" x 20" - 49115
18 gauge steel
\$94.49




28" x 20" - 49116
18 gauge steel
\$94.49



28" x 20" - 49117
18 gauge steel
\$94.49



28" x 20" - 49111
18 gauge steel
\$94.49



28" x 20" - 49112
18 gauge steel
\$94.49

Security



FG - 14" x 20" - 95463



PL - 10 x 14 - 95424



PL - 10 x 14 - 95419



PL - 10 x 14 - 95421



PL - 10 x 14 - 95414



PL - 10 x 14 - 95415



PL - 14 x 20 - 95496



PL - 14 x 20 - 95494



PL - 14x20 - 95481



PL - 14x20 - 95491



PL - 10 x 14 - 95502



PL - 10 x 14 - 95411



PL - 10" x 14" - 95465



PL - 10" x 14" - 95466



PL - 10" x 14" - 95470



PL - 14 x 20 - 95468



PL - 14 x 10 - 95410




FG - 24" x 18" - 95452

Temporary Signs

Professional looking, Temporary Signs warn of possible hazards in a cost-effective way.

- More than 30 stock legends available in various sizes
- Constructed of lightweight corrugated plastic material (B-836)



Lightweight corrugated plastic for indoor use or secured outdoor use.



B-836 - 18 x 24 - 78007



B-836 - 18 x 24 - 78004



B-836 - 18 x 24 - 78055



B-836 - 18 x 24 - 78003



B-836 - 18 x 24 - 78014



B-836 - 18 x 24 - 78002



B-836 - 18 x 24 - 78018



B-836 - 18 x 24 - 78037



B-836 - 18 x 24 - 78031

NEW!

Create Custom Traffic & Parking Signs Online

Create your own custom Traffic & Parking Signs in seconds, and avoid paying any set-up charges! Choose your sign's text, color, size, and material.


- "Symbol of Access"
- "No Parking"
- "Reserved For"



Try the Custom Design Tool at www.BradyID.com!

Easy as 1, 2, 3!

- 1) Select your category
- 2) Customize your product
- 3) Add to your shopping cart



Create custom products in minutes!

Ships in 24-48 hours!

Also available for Safety Signs!

Traffic Signs

www.BradyID.com

Safety Signs

Traffic Control



A New Manual on Uniform Traffic Control Devices (MUTCD) Eff. 1/16/2001

FEDERAL MUTCD STANDARD

No person shall install or maintain in any area of private property used by the public any sign, signal, marking or other device intended to regulate, warn or guide traffic unless it conforms to the MUTCD.

ALL TRAFFIC AND PARKING SIGNS MUST BE REFLECTIVE AND MEET MINIMUM REFLECTIVE STANDARDS

Minimum reflective standards required, no more non-reflective signs allowed.

Day/night inspection and maintenance of all signs is required

All signs must conform to the standard sizes, shapes and colors called for in MUTCD

ALL POSTS USED FOR MOUNTING MUST BE BREAKAWAY STYLE AND MOUNTED AT NEW MINIMUM MOUNTING HEIGHTS

All supports require breakaway sockets or posts

Minimum mounting height is 5' from the bottom of the sign to the top of the ground in rural or low-volume areas

Minimum mounting height is 7' from the bottom of the sign in urban or heavily traveled areas



FG - 18 x 18 - 75205
 FG - 24 x 24 - 75206
 FG - 30 x 30 - 75207
 B-959 - 18 x 18 - 94142
 B-959 - 24 x 24 - 94143
 B-959 - 30 x 30 - 94144
 B-959 - 36 x 36 - 94145



FG - 24" per side - 75062
 B-959 - 24" per side - 94148
 B-959 - 30" per side - 80072



B-959 - 30 x 30 - 80074
 B-959 - 36 x 36 - 80075



B-959 - 24 x 24 - 80076
 B-959 - 30 x 30 - 94150



B-959 - 18 x 30 - 94152



5 MPH
 FG - 24 x 18 - 75199
 B-959 - 24 x 18 - 94210

10 MPH
 FG - 24 x 18 - 75200
 B-959 - 24 x 18 - 94211

15 MPH
 FG - 24 x 18 - 75201
 B-959 - 24 x 18 - 94212

20 MPH
 B-959 - 24 x 18 - 94213

25 MPH
 B-959 - 24 x 18 - 94209



B-959 - 18 x 18 - 94181



B-959 - 18 x 18 - 80091



B-959 - 18 x 18 - 94185



FG - 24 x 24 - 75094



B-959 - 24 x 18 - 94199



B-959 - 24 x 24 - 80099



B-959 - 24 x 18 - 94197



B-959 - 24 x 18 - 94195



B-959 - 24 x 18 - 94190



B-959 - 24 x 18 - 80098



FG - 18 x 18 - 75178



B-959 - 24 x 24 - 94225



B-959 - 30 x 30 - 80070




B-995 - 24 x 24 - 80068



B-959 - 18 x 24 - 94237



FG - 14 x 20 - 75198
 B-959 - 18 x 12 - 80095



B-959 - 18 x 12 - 80109



B-959 - 18 x 12 - 80100



B-959 - 24 x 24 - 94234
 B-959 - 30 x 30 - 94235



B-995 - 30 x 30 - 80067



B-959 - 24 x 18 - 94240



B-959 - 18 x 12 - 80077



B-959 - 18 x 12 - 80106

Traffic Control (continued)

! OSHA Requirements

Notice: Chock Rear Wheels 1910.178(k) and (m)
 When trucks are loaded and unloaded, OSHA requires the brakes to be set and wheel chocks to be placed under the rear wheels to prevent the trucks from rolling while they are boarded with a forklift or other powered industrial truck.




B-959 - 24 x 24 - 94192



B-959 - 24 x 24 - 94163




FG - 24 x 24 - 75066



FG - 5 x 14 - 75063




FG - 14 x 20 - 75155



FG - 10 x 14 - 73424
 AL - 10 x 14 - 43413
 PL - 10 x 14 - 25836



FG - 10 x 14 - 75097
 PL - 10 x 14 - 25849



AL - 10 x 14 - 43448
 PL - 10 x 14 - 25871



FG - 14 x 20 - 75198
 AL - 10 x 14 - 43447



B-959 - 30" Dia - 94307



FG - 12 x 15 - 75212



FG - 10 x 14 - 70536



FG - 10 x 14 - 75211




FG - 14 x 20 - 70230



FG - 18 x 24 - 70218
 AL - 10 x 14 - 43422
 PL - 10 x 14 - 25845



AL - 10 x 14 - 43408



AL - 10 x 14 - 43416
 PL - 10 x 14 - 25839



FG - 10 x 14 - 70223
 AL - 10 x 14 - 43369
 PL - 10 x 14 - 25792



AL - 10 x 14 - 43382
 PL - 10 x 14 - 25805



FG - 7 x 17 - 69562



FG - 7 x 10 - 71178
 AL - 10 x 14 - 43431
 PL - 10 x 14 - 25854



FG - 18 x 12 - 75166



FG - 18 x 12 - 75140
 B-959 - 18 x 12 - 94116



B-959 - 18 x 12 - 94130



B-959 - 18 x 12 - 94119



FG - 18 x 12 - 94105
 B-959 - 18 x 12 - 94120



FG - 18 x 12 - 75143



FG - 18 x 12 - 75227



B-959 - 18 x 12 - 80078



FG - 10 x 14 - 47329
 AL - 10 x 14 - 43406
 PL - 10 x 14 - 25829



AL - 10 x 14 - 43400



AL - 10 x 14 - 43429



FG - 12 x 18 - 75190



FG - 12 x 18 - 75226



FG - 12 x 18 - 75086



AL - 10 x 14 - 43437

? Looking for Handicap Parking Signs? Turn to page 40.

Traffic Signs

www.BradyID.com

Traffic Control (continued)

High Intensity Traffic Signs

- High intensity, reflective aluminum, signs offer the highest day and night visibility
- Ideal for long-term outdoor use
- MUTCD compliant



95043 18" x 18" \$106.36
95044 24" x 24" \$164.38
95045 30" x 30" \$193.05
95046 36" x 36" \$251.27



95041 30" x 30" \$193.05



95039 30" sides \$193.05
95042 36" sides \$251.27

Traffic Control Paddles

- Traffic Control Paddles are made of aluminum providing durability for years of on-the-job use.
- Paddles are 18" octagons and weigh 2 lbs.
- For greater flexibility and increased visibility add the 5 foot long aluminum handle.




Style No.	Description	Price
57754	Stop (Red/White) & Slow (Orange/Black)	\$59.15
57755	Stop (Red/White) both sides	\$59.15
55784	5 foot Long Handle Extension	\$20.43

Roll-Up Signs & Stand

- Signs set up in seconds
- Fiberglass cross-braces in stands
- Stand has 4 adjustable telescoping legs to ensure stability
- Optional flag assembly and flags available

Catalog #	Description	Legend	Price
56799	36" Reflective Vinyl	Men Working	\$249.29
56798	36" Nonreflective Mesh	Men Working	\$92.70
56800	48" Nonreflective Mesh	Men Working	\$114.37
57070	36" Fiberglass Cross Brace	-	\$21.80
57071	48" Fiberglass Cross Brace	-	\$25.82
57067	Aluminum Sign Stand*	-	\$344.56

*Cross braces sold separately




Street Sign Accessories

4-Way Cross Piece

- Mount on top of another street sign for additional sign

Description	Catalog #	Price
4-Way Cross Piece	56681	\$18.38



Posts have 7/6" diameter holes on 1" centers that run the full length of the post on all four sides.

Galvanized Posts

- Galvanized steel posts are manufactured of a high tensile steel and finished with uniform coatings of zinc and clear acrylic to resist corrosion
- Attractive round posts are 16 gauge and 23/8" O.D.
- Square posts are 14 gauge and 2" x 2" tube size

Size	Description	Catalog #	Price
8'	Square	78998	\$80.95



BriteSide® Reflective Panels

- Turns a new or existing U-channel post into a reflective surface
- Highly-reflective diamond-grade material
- 3" w x 6' h panels are available in 3 colors
- Ships complete with mounting hardware


Catalog #	Size	Color	Qty	Price
95036	3" x 6'	Blue	1	\$93.11
95037	3" x 6'	Red	1	\$93.11
95038	3" x 6'	Yellow/Green	1	\$93.11



Movable Sign Posts

- 17" diameter, 35 pound cast iron base with 1/2" diameter, 48" pipe is pre-drilled for signs that are 18" x 18", 24" x 18", or 24" x 24" in size

Catalog #	Description	Price
86366	14" iron sign base & 48" post kit black	\$163.26
86345	17" iron sign base & 48" post kit black	\$226.70



Tuff-N-Light U-Channel Post

- Ideal for traffic and industrial signage
- Closed profile posts are 6 times torsionally stronger than steel posts
- Open profile posts for signs up to 12" x 18"
- Length is 8'

Catalog #	Size	Description	Color	Price
97208	8'	Closed profile	White	\$49.36
97210	8'	Closed profile	Green	\$49.36
97207	8'	Open profile	White	\$42.45
97209	8'	Open profile	Green	\$42.45



Sign Base

- Securely mounts with three expansion bolts
- Accepts U-channel Posts
- Cast aluminum base is 15" in diameter and includes post mount stub and hardware

Catalog #	Description	Price
86339	15" Diameter, Cast Aluminum	\$127.53



U-Channel Sign Posts

- Ideal traffic signs and utility signage
- Baked green enamel finish on hot-rolled, high-tensile strength steel
- Weight: two pounds per linear foot
- Hardware sold separately below
- 3/8" holes, 1" on center

Cat. No.	Length	Price
95047	6'	\$28.17
97204	8'	\$35.47
97205*	10'	\$50.78
97206*	12'	\$54.61
87982	Post Driver	\$230.54

*Posts will ship via motor freight



Mounting Tape

- Indoor/Outdoor B-156 double-faced foam tape
- Bonds well to rough, irregular surfaces
- Service range: 50°F to 180°F
- Roll mounted 1/16" thick foam tape

Catalog #	Size	Qty	Price
78273	3/4" x 36 yds.	1 roll	\$54.24
19811	1" x 36 yds.	1 roll	\$61.93



Fence Sign Support Brackets

- Easily attaches signs to fences
- Brackets are constructed of 14 gauge steel with a green baked enamel finish
- 17" bracket fits signs 18" x 12" or 18" x 18"

Catalog #	Description	Price
86337	17" Bracket w/hardware	\$7.59



Vandal-Proof Tufnut™

- Plated steel nut secures tightly to prevent sign theft
- 3/16" nut for use with U-Channel Sign Posts (sold above)
- Set includes: 2 bolts, 2 washers and 3 Tufnuts™

Catalog #	Description	Price
97211	2 Bolts, 2 Washers, 3Tufnuts	\$11.96

Safety Posters

www.BradyID.com


Safety Signs

Laminated Safety Posters

- Concise, easy to understand safety posters are designed to provide continued reinforcement of your ongoing safety program
- All posters are laminated on both sides
- Plexi-glass holder (sold separately) allows you to store different posters and rotate them accordingly to your safety program



Catalog #	Description	Size and Material	Price Each
SH1824	Clear Plexi-glass Holder	18" X 24" Plexi-glass	\$56.21
MSSP	Machine Safety Poster	18" X 24" Laminated Paper	\$23.70



Catalog #	Description	Size and Material	Price Each
53200	Right To Know	18" X 24" Laminated Paper	\$33.83
53201	Right To Know - Spanish	18" X 24" Laminated Paper	\$33.83




Catalog #	Description	Size and Material	Price Each
53119	Haz Mat Warning	18" X 24" Laminated Paper	\$33.83



Catalog #	Description	Size and Material	Price Each
PS128E	Emergency First Aid	18" X 24" Laminated Paper	\$25.64



Catalog #	Description	Size and Material	Price Each
PS125E	Bloodborne Pathogens	18" X 24" Laminated Paper	\$25.64
PS125S	Bloodboam Pathogens - Spanish	18" X 24" Laminated Paper	\$25.64



Catalog #	Description	Size and Material	Price Each
LOSP8	Lockout Safety	18" X 24" Laminated Paper	\$25.89
LOSP8SP	Lockout Safety - Spanish	18" X 24" Laminated Paper	\$25.89



Catalog #	Description	Size and Material	Price Each
50344	Confined Space	18" X 24" Laminated Paper	\$31.92



Catalog #	Description	Size and Material	Price Each
FLSP	Forklift Safety	18" X 24" Laminated Paper	\$25.64



Catalog #	Description	Size and Material	Price Each
53202	Hazardous Material	22" X 26" Flexible Plastic	\$58.05



Catalog #	Description	Size and Material	Price Each
PS127E	Personal Protection	18" X 24" Laminated Paper	\$25.64



Catalog #	Description	Size and Material	Price Each
FESP	Fire Extinguisher Safety	18" X 24" Laminated Paper	\$25.64



Catalog #	Description	Size and Material	Price Each
BLSB	Back Lift Safety	18" X 24" Laminated Paper	\$25.63

Safety Posters and Banners

www.BradyID.com

OSHA Safety Poster

- OSHA notices and other essential safety information on one poster!
- Laminated for protection against vandalism and environmental damage
- Size: 25½" H x 39½" W

Poster contains:

- OSHA 300A form summary
- Employee Right to Job Safety & Health notice
- Access to Medical & Exposure Records notice
- OSHA "It's the Law" notice
- Emergency phone number chart
- Bloodborne pathogens and needlestick safety guide
- Safety training notice and 1-year safety meeting calendar
- Hazardous materials guide and customizable MSDS chart
- Customizable personal protective equipment chart



Catalog #	Description	Price Each
106434	OSHA Safety Poster	\$48.07

Safety Banners

- Constructed of heavy duty 10mil Vinyl (Indoor use only)
- Banners are 3.5' x 10'
- Price is \$291.25 ea.



Cat. No. 50901



Cat. No. 50904



Cat. No. 50907



Cat. No. 50910



Cat. No. 50902




Cat. No. 50905



Cat. No. 50908



Cat. No. 50911



Cat. No. 50900



Cat. No. 50903



Cat. No. 50906



Cat. No. 50909



Cat. No. 50912

Two easy ways to order Custom Signs:



**Online Customizing
is easy as 1, 2, 3!**

- 1) Select your category
- 2) Customize your product
- 3 Add to your shopping cart.

Customize & Order Through Your Distributor

- Customize your signs with your logo or other custom graphics
- Make signs up to 80" wide
- Print banners with full-color photos
- Print on special order materials up to 1.5" thick
- UV ink with 5-7 year life span
- Print Graphical Lockout Procedure Placards

- *OR* -

Customize & Order at www.BradyID.com with the new Custom DesignTool

Create made-to-order OSHA and ANSI Safety Signs or Traffic & Parking Signs for your facility with this easy-to-use application. Create signs in seconds and avoid paying any set-up charges. Quickly choose

- Customize and order signs 24 hours a day
- 11 Headers in English & Spanish
- 9 Categories of Pictograms
- 5 Sign Material Choices: Polyester, Vinyl, Plastic, Aluminum, Fiberglass
- Ships within 48 hours of ordering

Try the Custom Design Tool at www.BradyID.com!

NEW!

Create Custom Signs and More!

Brady's custom design tools are your online solution for creating unique signs, valve tags and property ID tags.

Choose the custom sign shop tool of your choice and in just a matter of minutes, you'll be creating a professional sign, tag or marker that your facility needs.

The made-to-order process lets you see the sign or tag as it's created, while you select the pictograms and text that make up your customized safety signs and tags.

Design custom products in minutes at
www.BradyID.com



Traffic Signs



Safety Signs



Tags



Pipe Markers



Property ID Tag



Graphical Lockout/Tagout Procedures

Your custom products ship in 24-48 hours!

Custom Signs / Material Descriptions / Pictos

www.BradyID.com

Safety Signs

MATERIAL DESCRIPTION

Premium Fiberglass Signs: (B-120) – Our highest quality, longest lasting sign material. Guaranteed not to chip, fade, rust, shatter or peel for 15 years. Sign legend is embedded within the sign panel, protecting it on both sides from weathering, abrasion, impacts and chemicals. Ideal for indoor or outdoor use. The sign is 0.100" thick. Service temperature range is -40°F to 190°F. It has rounded corners with 3/16" mounting holes.

BradyLam™ Signs: (B-140) – The BradyLam™ sign legend is printed on polyester film that is permanently bonded to a fiberglass backing. The sign is then over-laminated with Tedlar® to protect the graphics. The sign legend is protected from UV light, dirt and harsh chemicals. The sign is guaranteed indoors and outdoors for 15 years (dependent on user definition of failure and climatic conditions). Fiberlam signs are 0.11" thick and have a service temperature of -40°F to 212°F. They have rounded corners with 3/16" mounting holes.

High-Performance Polyester: (B-302) – Self-Sticking Laminated Polyester signs are surface-printed polyester with a polyester over-laminate. These signs are particularly suited for outdoor applications (8 years) and in harsh environments where excellent abrasion and chemical resistance is required beyond an unprotected surface-printed label. The SS Laminated Polyester signs have a cold temperature, permanent adhesive that makes the sign able to be applied in temperatures as low as 0°F on almost any shape or surface. The average thickness is 0.008", and the service temperature is -40°F to 230°F.

BradyLex™ Signs: (B-320) – BradyLex™ signs are made of Lexan® and Tedlar® PVF film. This combination is bonded to a rigid fiberglass panel. This total construction is strong as well as resistant to corrosion and abrasion. It is 0.070" thick and the graphics are protected. There is an average outdoor durability of 8 years. The service temperature range is -40°F to 175°F. Radius corners with 3/16" grommets holes.

Self-Sticking BradyGlo™ Polyester Signs: B-324 – Legend is printed on the 0.008" polyester film with acrylic adhesive. Charging time is 5 minutes at 1000 lux of light (60 mins. at 54 lux). BradyGlo™ Polyester is non-toxic, non-radioactive and explosion safe allowing for sanitary disposal. This product glows for +10 hours after the lights go out. Exceeds the following standards: ASTM, IMO, ISO/CD, PSPA, DIN, NFPA and OSHA. There is a 5 year life on the adhesive and the printed legend. The glowing properties of the sign never expire. Not recommended for outdoor applications. Service temperature range is -40°F to 230°F. Minimum application temperature of 50°F. Square corners without holes.

BradyGlo™ Plastic Signs: (B-347) – Legend is printed on polyester film that is applied to rigid polystyrene. Total product thickness is 0.041". Charging time is 5 minutes at 1000 lux of light (60 mins. at 54 lux). BradyGlo™ Plastic is non-toxic, non-radioactive

and explosion safe allowing for sanitary disposal. This product glows for +10 hours after the lights go out. Exceeds the following standards: ASTM, IMO, ISO/CD, PSPA, DIN, NFPA and OSHA. There is an expected 5 year service life on the printed legend. There is a consistent glow life and unlimited rechargability throughout the service life. Not recommended for outdoor applications. Service temperature range is -40°F to 194°F. Has square corners with 3/16" mounting holes.

BradyGuard™ Signs: (B-382) – BradyGuard™ signs are sub-surface printed. The two-ply reinforced construction makes it resistant to impacts, abrasion, chemicals and corrosion. BradyGuard™ sign legends are printed on the backside of clear acrylic that is then bonded to a fiberglass panel, protecting the legend. Total thickness is 0.100". Good durability in harsh and extreme environments, indoors and outdoors -40°F to 175°F. Rounded corners with four 3/16" grommets mounting holes.

Plastic Signs: (B-401) – The legend on this polystyrene sign construction is protected with a clear coat for increased chemical and abrasion resistance. This strong plastic sign is easy to handle, mount and store. Signs stay legible for up to 2 years outdoors, even in the harshest conditions. The total construction is 0.063" thick. Service temperature is -20°F to 150°F. Corners are rounded with 3/16" mounting holes.

Polyethylene Plastic Signs: (B-450) – Polyethylene plastic signs are linear polyethylene sheets containing UV light stabilizers that are surface printed. These signs are 0.055" thick. The average outdoor durability is 3 to 5 years. Is flexible enough to be mounted on curved areas. Service temperature is -40°F to 180°F. Square corners with 3/16" holes (high visibility signs have 2 keyhole slots on each side).

Aluminum Signs: (B-555) – Aluminum signs are made of 0.040" aluminum panels. The legend is printed on the aluminum panel and protected with a clear coat film. This durable sign construction has superior abrasion and chemical resistance indoors or outdoors. Stands up to spills, wash-downs and cleanings. The average outdoor durability is 5 to 8 years. Service temperature of -40°F to 212°F. Radius corners with 3/16" mounting holes.

Polystyrene Signs: (B-793) – The legend of a Polystyrene sign is printed onto a 0.060" thick surface. These economical signs have good impact resistance but should not be exposed to chemicals. The Polystyrene material is slightly flexible. The average outdoor durability of Polystyrene signs is 1 to 3 years. Service temperature of -30°F to 165°F. Square corners without holes. Used for vehicle placards which are slid into holders.

Magnetic Vinyl Signs: (B-811) – Magnetic Vinyl signs are used as temporary, reusable and movable signs. The legend is printed onto a vinyl surface that is bonded to a magnetic sheet. The total thickness of this construction is 0.025". The average outdoor durability is 2 to 4 years. Service temperature of 0°F to 158°F. Square corners without holes.

Self-Sticking Vinyl Signs: (B-946) – Self-Sticking Vinyl signs are printed with weather resistant inks and are particularly suited for use in outdoor applications where weatherability is a key consideration (5 year durability). The material is 0.005" thick and has a permanent cold temperature adhesive. The application temperature is as low as 0°F. Service temperature of -40°F to 180°F. Square corners without holes.

Reflective Aluminum Signs: (B-959) – Reflective Aluminum signs are primarily used for traffic control. The legend is printed onto the engineer-grade reflective sheeting that is then applied to an aluminum panel. The total thickness of the sign can range from 0.042" to 0.090" depending on size for added strength. These signs meet the MUTCD requirement for reflectivity. Reflective Aluminum signs are corrosion and rust resistant. The average outdoor durability of this sign is 7 years. Service temperature of -40°F to 180°F. Radius corners with four 7/32" corner holes or two centered 3/8" post holes.

Diamond-Grade™ Reflective Aluminum Signs: (B-995) – Diamond-Grade™ Reflective Aluminum signs are primarily used for traffic control. The Diamond-Grade™ Reflective material provides ultimate luminance and visibility, even during daytime hours. The legend is printed on the Diamond-Grade™ Reflective sheeting which is then applied to the aluminum panel. Total sign thickness is 0.097". Meets MUTCD, ASTM E-810 for coefficient of retro-reflection, and ASTM E-811 for nighttime color. Accepted by the FHWA and the DOT. The average outdoor durability of this sign is 7 years. Service temperature of -40°F to 212°F. Radius corners with four 7/32" corner holes or two centered 3/8" post holes.

Self-Sticking BradyLite® Reflective Vinyl Signs: (B-997) – BradyLite® Reflective Sheetting is excellent for use outdoors in cold climates. The cold temperature adhesive can be applied in temperatures as low as -10°F. It has excellent weatherability (4 to 6 year outdoor life). The reflectivity meets MUTCD requirements. The total thickness of this construction is 0.007". Service temperature of -40°F to 200°F. Square corners without holes.

PICTOGRAMS

- | | | | | | | | | | | | |
|----------------------|----------------------------|--------------------|--------------------------|-----------------------|-----------------|--------------------------|-----------------------|----------------------|--------------------------|----------------------------|----------------------|
| 1. Ear Protection 1 | 39. Ear Protection 2 | 2. Eye Protection | 3. Head Protection 1 | 61. Head Protection 2 | 4. Slip | 5. Respirator | 6. Confined Space | 7. Lockout/Tagout | 8. Pinch Rollers | 75. Pinch Press | 9. Cut/Sever |
| 12. Flammable 1 | 13. Flammable 2 | 52. Flammable 3 | 14. Stop | 15. Unauthorized | 16. Keep Out | 17. No Smoking | 18. Fire Extinguisher | 19. Eye Wash Station | 20. Radiation | 21. No Parking | 22. Low Clearance |
| 23. Cleanliness | 24. No Food/Beverage | 25. Air Respirator | 26. Apron | 27. Down Arrow | 28. Left Arrow | 29. Right Arrow | 30. Up Arrow | 31. Biohazard | 32. Boots | 35. Corrosive (Triangle) | 36. Corrosive |
| 38. Dust Mask | 41. Electrical 1 | 42. Electrical 2 | 43. Electrical 3 | 44. Explosive | 45. Eye Glasses | 49. Fire Hose | 53. Fork Lift | 54. Face Shield | 55. Full Protection Suit | 56. Gloves | 57. Goggles 1 |
| 58. Goggles 2 | 62. Hot Surface | 64. Laser | 66. Lockout/Tagout (Tag) | 68. Men | 69. Men/Women | 70. No Admittance | 71. No Entry | 77. Poison | 78. Recycle | 80. Safety Cross in Circle | 81. Safety Shoes |
| 84. Telephone | 85. Trip | 88. Women | 89. Static Picto | 90. Smoking | 92. Parking (P) | 93. No Parking (P) | 98. Fire Extinguisher | 99. Do Not Enter | 100. Safety Cross 2 | 101. Radiation Tripod | 102. Radiation Burst |
| 103. No Admittance 2 | 104. No Cell Phones/radios | 105. No Cell Phone | 106. No Guns | 107. No Camera | 108. Stop Sign | 109. Surveillance Camera | | | | | |

Custom Sign Order Form

www.BradyID.com

Order Quote Artwork Attached Ship Via: _____ P.O. # or Request # : _____

General Information - Fax completed form to your local distributor

Company Name: _____ Name: _____
Address 1: _____ Phone #: _____
Address 2: _____ Fax #: _____
City: _____ ST: _____ Zip: _____ Email: _____

Item Information

1. Material:

- Premium Fiberglass (B-120)
- Self-Sticking High Performance Polyester (B-302)
- Self-Sticking BradyGlo (B-324)
- BradyGlo Plastic Signs (B-347)
- Plastic Signs (B-401)
- Aluminum Signs (B-555)
- Magnetic Vinyl Signs (B-811)
- Reflective Aluminum Sign (B-959)
- Self-Sticking BradyLite Reflective Sign (B-997)
- Other _____ Material List (pg 56) and enter B# here

2. Header: (English / Spanish)

- | | |
|--|---|
| <input type="checkbox"/>  | <input type="checkbox"/>  |
| <input type="checkbox"/>  | <input type="checkbox"/>  |
| <input type="checkbox"/>  | <input type="checkbox"/>  |
| <input type="checkbox"/>  | <input type="checkbox"/>  |
| <input type="checkbox"/>  | <input type="checkbox"/>  |
- No Header (Fill in colors below)
_____ on _____
(Text Color) (Background Color)
Lower text will be black unless specified.

3. Size: (Height x Width)


- 3 1/2" x 5" 5" x 7"
- 4" x 6" (B-302 & B-946 only)
- 7" x 10" 9" x 12"
- 10" x 14" 12" x 18"
- 14" x 20" 18" x 24"
- Other: _____ x _____
(Height) (Width)

4. Quantity: _____


5. Pictogram #: _____

(See previous page then enter # here)

6. Finishing:

- No Holes
- 4 Corner Holes 2 Post Holes
- Foam Tape 2 Side Holes
- Other Show required hole placement in the box to the right 

Draw sign layout and text in box below (show picto placement if applicable)

7. 


Brady to arrange Layout as shown

Distributor Information

Distributor: _____ Contact: _____
Account #: _____ Fax #: _____ Phone #: _____

Safety Information Centers

www.BradyID.com/safetycenters



Right To Know Compliance Center

- Compliance center includes red polystyrene board, binder rack and MSDS binder (2023)
- 1.5" MSDS binder w/ 300 sheet capacity
- Center size: 20"H x 14"W x 4 1/2"D

Catalog #	Description	Price
2010	Compliance Center	\$72.96
RK018A	Compliance Center w/inserts	\$86.96
2010NB	Compliance Center w/o binder	\$57.33
2010SP*	Spanish Compliance Center	\$71.55

*Board is Spanish with Bilingual Binder (2026)



Double Right To Know Compliance Center

- This center includes red polystyrene board, 2 binder racks and two MSDS binders
- Center size: 20"H x 29"W x 4 1/2"D

Catalog #	Description	Price
2010DB	Double RTK Compliance Center	\$138.42
2010DBSP	Spanish Double RTK Center*	\$138.42


*Board is Spanish with Bilingual Binder (2026)



Economy Right To Know Center

- Includes MSDS "V" sign, 8"H x 14 1/2"W x 6"D
- 1.5" MSDS binder w/ 300 sheet capacity

Catalog #	Description	Price
2007	Economy RTK Center	\$83.78
RK085A	Rack & Binder w/inserts	\$62.66
2005	Rack & Binder Only	\$51.73



Binder Holders

- PVC coated steel racks designed for holding binders up to 3" ring diameter
- Size: 9"H x 14"W x 4 1/2"D

Catalog #	Description	Price
2014	Yellow Binder Holder	\$31.85
2014W	White Binder Holder	\$31.85



Standard Right To Know Center

- Tough acrylic RTK board can hold up to 100 training booklets and our largest MSDS binder
- Includes our 1 1/2" binder and 10 training booklets
- Center size: 30"H x 24"W x 4 1/2"D

Catalog #	Description	Price
2001	Standard Right to Know Center	\$148.21
2012	Board Only	\$118.65
2002	Bilingual version*	\$148.21

*includes 5 English booklets, 5 Spanish booklets and a bilingual binder



MSDS Metal Cabinet

- Made of 20 gauge powder coated steel
- Wall mountable
- Front panel pulls down to reveal a guide to Haz-Mat labels
- Equipped center includes:
 - 2 - 2 1/2" MSDS Binders (2024)
 - 25 - Right To Know training booklets (2101)
 - 1 - Binder training insert (BR801B),
- Cabinet size: 22 1/2"H x 26 1/2"W x 6"D

Catalog #	Description	Price
RK623E	MSDS Metal Cabinet	\$301.61



MSDS/Job Site Safety Document Center

- Holds one 3-ring binder in a very rugged, weather resistant and lockable polystyrene case.
- Table top or wall mount.
- Center size: 13 1/2"H x 13 1/2"W x 4 3/4"D

Catalog #	Description	Price
JS1	MSDS/Job Site Center	\$183.67



Job Site Center

- Includes Job Site binder with fold away handles.
- Binder has 2 sets of 1" nylon rings that will hold approximately 400 pgs.
- PVC coated wire rack can be mounted anywhere you need it.
- Center size: 12 1/2"H x 14"W x 4 3/4"D

Catalog #	Description	Price
2032	Job Site Center	\$55.22
2022	Job Site Binder Only	\$36.13



Suggestion Box

- Black acrylic box w/ a lockable top & side pocket
- Pocket measures 5"H x 4"W x 1 3/8"D
- Top drop slot is 9" wide. Wall or table mount
- Box Dimensions: 12"H x 11 3/4"W x 4 3/4"D

Catalog #	Description	Price
MC111E	Suggestion Box	\$104.09



Standard MSDS Binders

- 1 1/2" diameter rings hold 275-300 sheets, 2 1/2" diameter ring holds 400-500 sheets and 3" diameter ring hold 600 sheets
- These binders have a durable Polyethylene cover, 36" chain and pair of sheet lifters

Catalog #	Description	Price
2023	Standard Binder (1 1/2" ring)	\$20.79
2024	Bigger Binder (2 1/2" ring)	\$29.08
2025	Biggest Binder (3" ring)	\$30.45
2026	Bilingual Standard Binder (1 1/2" ring)	\$20.79
2027	Bilingual Bigger Binder (2 1/2" ring)	\$29.08
2028	Bilingual Biggest MSDS Binder (3")	\$30.45

*Insert is catalog #BR801B



MSDS Training Binder Insert

This detailed binder insert package contains:

- OSHA Haz-Com Standard highlights and overview of program requirements
- Compliance checklist
- Two 15 page RTK training booklets,
- Mini RTK poster (Spanish/English)
- 50 clear sheet protectors
- A-Z index tabs
- Binders sold separately to the left

Catalog #	Description	Price
BR801B	Binder Insert	\$13.51



Information Centers

- Rugged red poly backboard comes with white PVC coated wire basket, allowing for high visibility and convenience of holding important papers
- Tear resistant 3-ring binder holds approx 300 sheets and comes with chain
- Mounting hardware included
- Center size: 20"H x 14"W

Catalog #	Description	Price
IC326E	Emergency Information Center	\$71.55



Standard Operating Procedures Center

- Poly backboard w/ white PVC coated wire basket
- Rugged binder holds approximately 300 sheets and comes with an attached chain
- Binders are available separately

Catalog #	Description	Price
SM681A	Procedures Center	\$76.14
SM682A	Double Standard Operation Procedures Center	\$137.08



Bloodborne Pathogen Compliance Center

- Highly visible display also includes a 1½" diameter 3 ring binder holds up to 300 pages of your exposure control plans (not included)
- Wall mount only
- Center size: 20"H x 14"W x 4½"D

Catalog #	Description	Price
BH2010	Compliance Center	\$112.94



Lockout Procedure Station

- Backboard made from durable polystyrene
- Includes pre-drilled holes and hardware for wall mounting
- 3-ring, 1.5" binder made from 55 gauge polyethylene
- Backboard dimensions: 20"H x 14"W x 4.5"D

Catalog #	Description	Price
LOSP22	Station With Binder & 25 Forms	\$78.82
99289	Lockout Procedure Station With Binder Only	\$73.55
LOSB1	Lockout Procedure Binder Only	\$18.03



Sign/Permit Holder & Entry Permits

- Provides a confined space warning and easy access to permits
- Holds 8½" x 11" forms
- Made of durable polycarbonate material
- Holder dimensions: 12" x 19"
- Permits/forms sold separately

Catalog #	Description	Quantity	Price
65903	Permit Holder	1	\$98.10
65937	2-ply Carbonless	25 pk	\$30.56



Safe-T-Grip® Fuse Pullers

- Provides maximum convenience when removing or replacing cartridge fuses
- Notched handles for no-slip grip
- Clearly marked amperage ranges
- Exceeds MIL specifications

Catalog #	Description	Price Each
65280	(C) For 0-100A, 250V & 600V: 7½" long	\$14.84



Battery Cleaning & Charging Safety Kit

- Help minimize the risk of employee acid burns or shocks while charging batteries
- Fully equipped portable kit includes: (1) pair of large unsupported neoprene over natural rubber gloves; (1) pair of clear chemical goggles with indirect ventilation; (1) black rubber apron, 45" x 35"; (1) 8" synthetic brush; (2) 9¼" x 14½" chemical sorbent pads for small spills; (1) quart neutralizing and cleaning agent with trigger sprayer; (1) laminated instruction card

Catalog #	Description	Price
BCK	Battery cleaning & charging kit	\$125.03



E-Z Check® Plus GFI Circuit Tester

- Checks for the following conditions: correct wiring, open ground, reverse polarity, open hot, open neutral, hot on neutral, hot and ground reversed with open hot, and ground fault interruption

Catalog #	Description	Price
65273	E-Z Check® Plus GFI Circuit Tester	\$56.85




Hazard Communication OSHA Standards

The Occupational Safety and Health Administration (OSHA) Federal Hazard Communication Standard 29 CFR 1910.1200 has become known as the "Right-To-Know" law. This standard gives both employers and employees a right-to-know about the hazardous chemicals they use in the workplace. It is designed to reduce the incidence of chemical source injury and illness in the workplace. In order to accomplish this, employers are required to:

1. Have Material Safety Data Sheets (MSDS) on file for every hazardous chemical in the workplace available to all employees during their work shift.
2. Train employees about the potential hazards, how to identify and safely work with hazardous chemicals and the proper personal protection necessary when working with hazardous chemicals. Employees must be trained before they start a work assignment.
3. Identify and list all of the hazardous chemicals in the workplace.
4. Have a written hazard communication program available for employees, OSHA and outside contractors who enter the workplace.

5. Have labels on all hazardous chemical containers that:
 - List the name and address of the manufacturer
 - List the chemical name
 - List the type of potential hazard that exists
 - List the precautions necessary
 - List target organ information
 - Are easily related to the appropriate MSDS on file
6. Maintain reports, records and logs for the entire program.
7. Certain states require that you report all of this information to a state agency, department of labor, health department or fire department depending on the state law that is in effect.


Hard work is necessary to come into compliance with the law. Brady offers a wide variety of products to keep your work to a minimum, while enabling you to implement a complete program that will bring your company into compliance with the Hazard Communication Standard.



NFPA




HMIG Color Bar



NFPA



HMIG Color Bar



5" x 3" Container Labels

- Economical option for secondary container labeling
- Choose from paper or vinyl materials in NFPA Diamond or HMIG Color Bar formats
- Standard package: 500 labels per roll

Catalog #	Material	Format	Price
58260	Paper	HMIG Color Bar	\$51.54
58261	Vinyl	HMIG Color Bar	\$114.12
58262	Paper	NFPA	\$51.54
58263	Vinyl	NFPA	\$114.12

2" x 1¼" Laboratory Labels

- Choose from paper or vinyl materials in NFPA Diamond or HMIG Color Bar formats
- Write-on labels allow you to customize your message.
- Standard package: 500 labels per roll

Catalog #	Material	Format	Price
58268	Paper	HMIG Color Bar	\$24.08
58269	Vinyl	HMIG Color Bar	\$48.15
58270	Paper	NFPA	\$24.08
58271	Vinyl	NFPA	\$48.15

Write-On Right-To-Know Labels

- Customize these Blank R-T-K Labels by writing your own message on them and adding R-T-K pictograms.
- 50 Per Package

Catalog #	Material	Format	Size	Price
58700	B-933	NFPA	3" x 5"	\$51.93
58703	B-933	Color Bar	3" x 5"	\$51.93



MarkWare™ Software

- Use MarkWare™ Software (sold separately) to create your own Right-To-Know Container Labels
 - Compatible for use with most laser printers
- Visit www.BradyID.com or view page 156.



Hazard Communication (RTK)

www.BradyID.com



Blank NFPA Placards

- Place directly on storage tanks, processing tanks and vessels, feed hoppers, pipelines and other potentially hazardous equipment
- Meets National Fire Protection Association's Code No. 704M and Federal Standard 313
- Add Gothic style Quik-Align® numbers and letters (sold separately) to mark the corners

Catalog #	Material	Size	Qty	Price
58656	B-120 Fiberglass	11" sq.	1	\$31.54
58510	B-120 Fiberglass	16" sq.	1	\$41.40
58501	B-946 Vinyl	5" sq.	10	\$32.66
58502	B-946 Vinyl	7½" sq.	10	\$51.40
58503	B-946 Vinyl	10" sq.	10	\$121.57
58504	B-946 Vinyl	15" sq.	10	\$233.15



HMIG Labels Station

- Acrylic Station has 6 - 3/4" pockets for holding sheet labels, 1 - 5" dowel to hold label rolls and a pen holder
- Provides hazard rating information printed on board
- Station size is 11" H x 18" Wide

Catalog #	Description	Price Each
PD674E	Prinzing Large HMIG Label	\$155.33



NFPA Placard Kits

- Vinyl kits come complete with 10 blank NFPA placards, and 10 characters each of 0 - 4, W, ☠, OXY, ACID, COR and ALK
- Fiberglass kits come complete with 1 blank NFPA placard, and 10 characters each of 0 - 4, W, ☠, OXY, ACID, COR and ALK

Catalog #	Material	Placard Size	Charac. Size	Price
50053	B946 Vinyl	10" sq	4"	\$214.64
50055	B120 Fiberglass	11" sq	4"	\$144.43
50054	B946 Vinyl	15" sq	6"	\$350.07
50056	B120 Fiberglass	16" sq	6"	\$228.39


CHEMICAL NAME	PROTECTIVE EQUIPMENT GUIDE	
HEALTH	A	G
FLAMMABILITY	B	H
INSTABILITY	D	J
PROTECTIVE EQUIPMENT	E	K
	F	X

Ask your supervisor for special handling instructions.

HMIG Self-Laminating Labels

- Label and overlay all in one - self-adhesive polyester label includes polyester laminate cover.
- Write in the appropriate rating on the left side. The right side shows the index for required ppe.


Catalog #	Size	Qty	Price
60332	2" x 3½"	25/pack	\$26.64
60333	3" x 5"	25/pack	\$28.42



NFPA Diamond Labels

- Available in rolls of 500


Catalog #	Material	Size	Price
53072	Vinyl	6" x 6"	\$312.51



Hazardous Info Placards

- Placards graphically explain the NFPA Hazard Identification Coding System
- B-120 premium fiberglass

NFPA Version			
Cat.No	Material	Size	Price
78788	B-120	10" x 14"	\$25.61



Front

RTK Wallet Card

- Handy reference of the NFPA Hazard identification Coding System
- Ideal for distribution to employees following formal hazard communication training
- Card size: 2 1/8" x 3 3/8"

Catalog #	Description	Qty	Price
58515	RTK Wallet Cards - English	25	\$62.89
89257	RTK Wallet Cards - Spanish	25	\$64.76



GHS (Globally Harmonized System) Compliance

GHS is an acronym for the Globally Harmonized System. The GHS regulations are international regulations created by the United Nations for the Classification and Labeling of Hazardous Chemicals. The expectation is that the majority of countries globally will adopt and enforce most elements of the GHS through their regulatory agencies having jurisdiction for this public safety concern.

GHS Status in the U.S.

OSHA is expected to publish an updated Hazard Communications standard in September 2011, or shortly thereafter, that will incorporate the major elements of the GHS. A 3 year transitional period is expected to allow companies' time to fully implement the new standards in their facilities.

GHS Status around the World

The European Union is already well along the path to full implementation of GHS (referred to as CLP, Classification for Labelling & Packaging, by the EU), and countries in Asia are quickly following in its footsteps.

What is required to comply with the Hazard Communication Standard?


The basic requirements for OSHA's HazCom standard are:

- A written chemical hazard program
- Labels on containers
- Safety Data Sheets (SDS)
- Chemical hazard training for employees

Custom GHS Labels Available

All organizations that ship, receive, handle, and maintain potentially hazardous chemicals will be impacted by the new GHS standard.

- Create your own GHS-compliant labels through your MarkWare™ software on printers such as the Globalmark Industrial Printer. Visit www.BradyID.com/markware for more information
- Brady will also create and print custom GHS labels to your specific labeling requirements:
 - Create labels in English, Spanish, French and more
 - Available in a variety of sizes to fit your needs
 - Contact us at: 1-888-250-3082



Learn how to get your facility ready for GHS implementation with these free downloads from www.BradyID.com/GHS

- Safety Data Sheet (SDS) Requirements Document.
- Five Steps to Compliant Hazard Communication Program Whitepaper

Visit www.BradyID.com/GHS for more information and watch for the Brady GHS Product Brochure coming this fall!

Hazardous Waste Labels

www.BradyID.com

Hazardous Waste Labels

- Labels comply with all current Federal regulations regarding identification of hazardous waste materials for transportation off-site



Catalog #	Description	Material	Size	Qty	Price
63268	Hazardous Waste	Vinyl	6" x 6"	50	\$30.59
60448	Hazardous Waste	Vinyl	6" x 6"	100	\$58.95
63274	Non-Regulated Waste	Vinyl	6" x 6"	50	\$30.59
60452	Non-Regulated Waste	Vinyl	6" x 6"	100	\$58.95
63275	Non-Hazardous Waste	Vinyl	6" x 6"	50	\$30.59
60453	Non-Hazardous Waste	Vinyl	6" x 6"	100	\$58.95
63269	Hazardous Waste	Vinyl	4" x 6"	50	\$30.59
60451	Hazardous Waste	Vinyl	4" x 6"	100	\$58.95

Asbestos Labels


- Made of self-adhesive vinyl
- Standard package: 100 labels



Catalog #	Description	Size	Qty	Price
60240	Asbestos Labels	4" x 4"	100	\$18.69

PCB Markers


- Use PCB warning labels and signs to satisfy EPA 40 CFR Part 761 Subpart C for identification of PCB contaminated equipment or to mark PCB waste
- Made of B-946 self-sticking vinyl
- Standard package: 50 Identical Markers



Catalog #	Description	Size	Qty	Price
87028	EPA Reference 761.44(a)	6"x6" Vinyl	50	\$96.18

Universal Waste Labels


- Meet universal waste requirements, 40 CFR 273.14
- Standard package: 100 labels



Catalog #	Description	Size	Qty	Price
60351	Universal Waste Labels	6" x 6" Vinyl	100	\$58.95
60362	Universal Waste Labels	6" x 6" Paper	100	\$29.48

Waste Disposal Labels

- Use to easily identify and sort waste
- Available in B-933 self-sticking vinyl or B-235 economical paper
- Label size: 6" x 6"
- Choose from Standard Labels, if you want to write in your own information, or Custom Labels, if you would like us to pre-print them
- Standard package: 100 labels




Catalog #	Description	Qty	Price
60356	6" x 6" Vinyl	100	\$58.95




Catalog #	Description	Qty	Price
60360	6" x 6" Vinyl	100	\$60.65



Catalog #	Description	Qty	Price
60361	6" x 6" Vinyl	100	\$60.65




Catalog #	Description	Qty	Price
63240	6" x 6" Outdoor Vinyl	100	\$94.91



Catalog #	Description	Qty	Price
60352	6" x 6" Vinyl	100	\$60.65



Catalog #	Description	Qty	Price
60364	6" x 6" Paper	100	\$30.56




Catalog #	Description	Qty	Price
60355	6" x 6" Vinyl	100	\$58.95

Hazardous Material Shipping Labels

- Meets D.O.T. requirements HM-181 Regulation
- Label size: 4" x 4"
- Standard package: 500 labels per roll
- Price \$65.19

CLASS 2:



CLASS 3:



CLASS 8:



CLASS 9:



Vehicle Placards

- Placards meet D.O.T. Requirements HM-181 requirements
- B-946 self-sticking vinyl (SSV) placards may be applied directly to your vehicle
- Provide over 5 years outdoor durability
- Placards have square corners and no holes
- Placard size: 10¾" x 10¾"
- B-101 Economical 1.75 lb. polycoated tagboard (PT) placards exceed D.O.T.'s 30 day weather requirement



B-946 High Performance Vinyl

Catalog #	Legend	Price
63409	Flammable	\$4.54
60378	Flammable - Blank	\$4.54
63420	Corrosive	\$4.54
63407	Non-Flammable Gas	\$4.54
63332	Explosive 1.4S	\$4.54

B-101 Polycoated Tagboard

Catalog #	Legend	Price
63443	Flammable	\$1.54
60394	Flammable - Blank	\$1.40
63454	Corrosive	\$1.50
63441	Non-Flammable Gas	\$1.54

Custom Hazard Materials Shipping Labels Available

Custom Hazard Material Shipping Labels Available. Brady offers a variety of stock and custom hazard material shipping labels to fit your applications. Visit www.BradyID.com for the full product line.

Brady also offers a variety of other custom products including; signs, labels, tags, banners, display boards and pipe markers. For more information contact your local brady distributor.



Number & Letter Labels

www.BradyID.com



15 Series Numbers & Letters

- B-946 premium outdoor grade vinyl with permanent pressure sensitive adhesive
- Designed for permanent applications in severe outdoor environments as well as indoors. Special acrylic adhesive adheres strongly, making marker removal difficult

Catalog #	Markers Per Card	Charac. Height	Marker Size H x W	Price
1530.*	10	1"	1½" x 7/8"	\$3.23
1534.*	10	1½/16"	2¼" x 7/8"	\$3.57
1550.*	6	2½/16"	3½" x 1½"	\$4.86



Aluminum Utility Panels

- Twenty mil. (.020") aluminum panels are designed for ruggedness
- Flexible to conform to pole curve
- Standard package: 25 panels

Catalog #	Overall Size	Marking Size	Recom. Markers	Max. Markers	Price
97198	1¾" x 7¾"	1¾" x 6½"	B-946	8	
			B-997	8	\$37.50
97199	1¾" x 12"	1¾" x 11¼"	B-946	12	
			B-997	11	\$42.87



Indoor Numbers & Letters

- B-498 plastic coated cloth numbers & letters with pressure sensitive adhesive
- Black characters on a yellow background
- Permanent or Repositionable: once applied, numbers & letters are there to stay...unless you want to change them
- Order by card only

Catalog #	Markers Per Card	Charac. Height	Card Size H x W	Price
3410.*	78	3/8"	½" x 1½/32"	\$3.09
3420.*	32	5/8"	¾" x 9/16"	\$3.09
3430.*	10	1"	1½" x 7/8"	\$3.09
3440.*	10	1½/16"	2¼" x 7/8"	\$4.36
3450.*	6	2½/16"	3½" x 1½"	\$6.14
3460.*	5	3/8"	5" x 1¾"	\$9.05

Stock Cards: Numbers 0-9; Capital Letters A-Z; Dash; Arrows and Blanks available. Add the number or letter you need after the 4 digit number



Indoor Numbers & Letters Combo Packs

- B-498 plastic coated cloth tape with pressure sensitive adhesive
- Number packs contain all numbers from 0-9; number of cards vary according to their frequency of use
- Standard package: 25 assorted cards; 32 markers per card

Catalog #	Description	Card Size H x W	Charac. Height	Price
34251	Letters	¾" x 9/16"	5/8"	\$46.48
34252	Numbers	¾" x 9/16"	5/8"	\$46.48



Outdoor Numbers & Letters Combo Packs

- B-946 premium outdoor grade vinyl with permanent pressure sensitive adhesive
- Black characters on a yellow background
- Standard package: 25 assorted cards, 10 markers per card

Catalog #	Description	Card Size H x W	Charac. Height	Price
97602	Letters	1½" x 7/8"	1"	\$52.23
97603	Numbers	1½" x 7/8"	1"	\$52.23

 www.BradyID.com

Over 30,000 products now at your fingertips.

Visit the new BradyID.com, your online resource for:

- Full Product Offerings
- Product Info & Literature
- Product Demos
- Create Custom Products
- e-Learning Training Courses
- Whitepapers
- Webinars
- And so much more!



Indoor/Outdoor Numbers & Letters (B-946)

- Black Helvetica Medium characters on a white background
- Superior chemical resistance - resists oil, grease, water and mild solvents
- UV resistance
- Designed for permanent applications in outdoor environments as well as indoors.
- Superior abrasion resistance
- Stock cards: numbers 0-9; capital letters A-Z; dash

Cat. No.	Charc. Height	Marker Size	Markers per Card	Price
9712-*	5/8"	3/4" x 21/32"	20	\$3.09
9713-*	1"	1 1/2" x 1 1/16"	10	\$3.89
9714-*	1 15/16"	2 1/4" x 1 13/16"	5	\$4.53



Gothic Quick-Align® Kits

- B-933 vinyl film w/ permanent adhesive
- Self-spacing, self-aligning diecut characters
- Industrial grade vinyl resists temperature extremes, abrasion and common solvents
- Each kit contains: 20 each of A, E, I, L, N, O, R, S, T, and numbers 0-9; 10 each of remaining letters; and 5 each of \$, & and punctuation

Catalog #	Size	Color	Price
52203	1"	Black	\$266.45
52207	2"	Black	\$294.70
52211	3"	Black	\$378.73
52215	4"	Black	\$516.20



BradyLite® Reflective Numbers & Letters (B-997)

- Made from Engineering Grade B-997 BradyLite® Reflective Material - reflects light 100 times brighter than a plain white surface
- Will perform despite storms, snow, humidity and other tough environmental conditions
- **For Low Temperature Applications**
Can be applied at temperatures as low as 10°F
- Standard package: 25

Cat. No.	Marker Size H x W	Letter Height	Color	Price
5890-*	1 7/8" x 1 3/8"	1 1/2"	Yellow/black	\$22.96
5000-*	2 7/8" x 1 3/4"	2 1/2"	Yellow/black	\$28.45
5905-*	1 1/2" x 1"	1"	Yellow/black	\$20.84
5910-*	1 1/2" x 1"	1"	Black/orange	\$20.84



Gothic Quick-Align® Ten Packs

- B-933 vinyl film w/ permanent adhesive
- Order in 10 packs only, no broken packages
- Standard package: 10 identical characters or arrows per pack; five \$, & and punctuation per pack
- Refill your Quick-Align Kit (sold to left)

Catalog #	Size	Color	Price
5010-*	1"	Black	\$5.67
5050-*	2"	Black	\$6.16
5100-*	3"	Black	\$7.98
5140-*	4"	Black	\$10.83
5180-*	6"	Black	\$16.66



3-Series Glow-in-the-Dark/ Ultra Reflective Numbers & Letters

- 7x more reflective than other reflective materials
- Black characters w/ glow-in-the-dark border on a highly reflective silver background
- Glow-in-the-dark boarder illuminates character for distinct definition in blackout conditions
- Designed for permanent application in severe outdoor environments as well as indoors.
- Standard package: 10 identical characters

Catalog Number	Character Height	Marker Size	Price
3000-*	2"	2 7/8" x 1 1/2"	\$12.48
3010-*	3"	3 1/2" x 2 1/2"	\$15.45
3020-*	5"	6" x 3"	\$31.48



Magnetic Numbers

- Number height is 1 1/2"
- Perfect for safety scoreboards (see sign section)
- 15 each of 0-3, 8 each of 4-9
- 108/package

Catalog #	Character Height	Price
57624	1 1/2"	\$80.53

Arc Flash Labels

www.BradyID.com/arcflash

Labels and Tags

NFPA70 National Electric Code

110.16 Flash Protection

Switchboards, panelboards, industrial control panels, meter socket enclosures, and motor control centers that are in other than dwelling occupancies and are likely to require examination, adjustment, servicing, or maintenance while energized shall be field marked to warn qualified persons of potential electric arc flash hazards. The marking shall be located so as to be clearly visible to qualified persons before examination, adjustment, servicing, or maintenance of the equipment.

FPN No. 1:

NFPA 70E-2009, Standard for Electrical Safety in the Workplace, provides assistance in determining severity of potential exposure, planning safe work practices, and selecting personal protective equipment.

FPN No. 2:

ANSI Z535.4-1998, Product Safety Signs and Labels, provides guidelines for the design of safety signs and labels for application to products.

NEC-Compliant Arc Flash Labels

- Complies with NEC 110.16
- Made of durable B-302 polyester with overlaminates to withstand harsh environments.

2" x 4" Arc flash & shock hazard; table



Catalog #	Description	Qty.	Price
101517	2"x4" Warning	100/roll	\$79.42
101519	2"x4" Warning	10/pk	\$11.49
101518	2"x4" Danger	100/roll	\$79.42
101520	2"x4" Danger	10/pk	\$11.49

3.5" x 5" Text & pictogram



Catalog #	Description	Qty.	Price
102307	3.5"x5" Warning	100/roll	\$144.43
101950	3.5"x5" Warning	5/pk	\$11.58
102308	3.5"x5" Danger	100/roll	\$144.43
101951	3.5"x5" Danger	5/pk	\$11.58

NFPA 70E-Compliant Arc Flash Labels

- Complies with NEC and NFPA 70E
- Made of B-933 vinyl, which can be written on with a pen or marker.

2" x 4" Arc flash & shock hazard; table



Catalog #	Description	Qty.	Price
114171	2"x4" Warning	100/roll	\$79.42
114172	2"x4" Warning	10/pk	\$11.49
114174	2"x4" Danger	100/roll	\$79.42
114173	2"x4" Danger	10/pk	\$11.49

3.5" x 5" Text & pictogram



Catalog #	Description	Qty.	Price
114175	3.5"x5" Warning	100/roll	\$144.43
114176	3.5"x5" Warning	5/pk	\$11.58
114177	3.5"x5" Danger	100/roll	\$144.43
114178	3.5"x5" Danger	5/pk	\$11.58

Write-On Arc Flash Labels

- Write-in areas for equipment-specific information like flash protection boundary, hazard category, and required PPE.
- B-933 Vinyl can be written on with pen or marker.



4" x 6" Arc flash hazard

Catalog #	Description	Qty.	Price
99460	4"x6" Warning	5/pk	\$12.28
99461	4"x6" Danger	5/pk	\$12.28



5" x 7" Arc flash hazard & shock hazard

Catalog #	Description	Qty.	Price
99458	5"x7" Warning	5/pk	\$13.32
99459	5"x7" Danger	5/pk	\$13.32

Arc Flash Labels with Preprinted Hazard Categories

- Labels come with the hazard category and PPE requirements preprinted
- Write-in areas for specifics such as min arc rating, flash protection boundary, etc.
- B-933 Vinyl can be written on with pen or marker.



4" x 6" Arc flash hazard

Catalog #	Header	Hazard	Qty.	Price
99480	4"x6" Warning	0	5/pk	\$12.28
99482	4"x6" Warning	1	5/pk	\$12.28
99484	4"x6" Warning	2	5/pk	\$12.28
99498	4"x6" Warning	2*	5/pk	\$12.28
99486	4"x6" Warning	3	5/pk	\$12.28
99488	4"x6" Warning	4	5/pk	\$12.28
99481	4"x6" Danger	0	5/pk	\$12.28
99483	4"x6" Danger	1	5/pk	\$12.28
99485	4"x6" Danger	2	5/pk	\$12.28
99499	4"x6" Danger	2*	5/pk	\$12.28
99487	4"x6" Danger	3	5/pk	\$12.28
99489	4"x6" Danger	4	5/pk	\$12.28



5" x 7" Arc flash & shock hazard

Catalog #	Description	Hazard	Qty.	Price
99466	5"x7" Warning	0	5/pk	\$13.32
99468	5"x7" Warning	1	5/pk	\$13.32
99470	5"x7" Warning	2	5/pk	\$13.32
99621	5"x7" Warning	2*	5/pk	\$12.28
99474	5"x7" Warning	3	5/pk	\$13.32
99476	5"x7" Warning	4	5/pk	\$13.32
99467	5"x7" Danger	0	5/pk	\$13.32
99469	5"x7" Danger	1	5/pk	\$13.32
99471	5"x7" Danger	2	5/pk	\$13.32
99622	5"x7" Danger	2*	5/pk	\$12.28
99475	5"x7" Danger	3	5/pk	\$13.32
99477	5"x7" Danger	4	5/pk	\$13.32

NEW!

BBP®31 Sign & Label Printer

The NEW BBP®31 Sign & Label Printer can take on all your arc flash labeling needs! View page 132 for more information.



Arc Flash Training Aids

www.BradyID.com/arcflash

Promote awareness of the dangers associated with arc flash accidents and make sure your workers know how to protect themselves!

Labels and Tags

work live **Preventing Arc Flash Injuries**

Arc flash is a short circuit through air, that flashes over from one exposed live conductor to another, or to ground. Lightning is an example of a naturally occurring arc flash!

Arc flash is extremely dangerous and can cause traumatic injury or death!

Never work live without management approval and a complete understanding of the associated hazards and safe work practices.

What are Common causes of arc flash?

- Placing a conductive object too close to a high-voltage source of current
- Sparks from dropping tools, racking breakers, racking test die's
- Equipment failure due to the use of high-voltage components, improper installation or just normal wear and tear!
- Overlooking safety procedures
- Overlooking safety procedures
- Overlooking safety procedures

Tasks that may expose you to danger:

- Reenergizing or restoring power
- Working on control circuits
- Clearing capacitor banks in an MCC
- Testing a voltage reading
- Working in confined spaces
- Working in a control room
- Working on or near energized equipment
- Working on or near energized equipment
- Working on or near energized equipment

How to protect yourself and others:

- Whenever possible, working equipment before service and maintenance
- Configure a hazard assessment and follow approved safe work practices.
- Wear appropriate protective clothing and equipment (see chart).
- Use insulated gloves, tools, materials, and devices.
- Have a qualified person (based on the flash protection boundary) perform the work.
- Use appropriate PPE based on the hazard level.
- Use appropriate PPE based on the hazard level.
- Use appropriate PPE based on the hazard level.

Arc Flash Hazard Categories & Personal Protection Requirements

Hazard Category	Minimum Arc Rating (cal/cm²)	Required PPE	Required PPE	Required PPE	Required PPE
0	N/A	Long-sleeve shirt and long pants (natural fibers)	Safety glasses or safety goggles	Hearing protection (ear canal inserts)	Leather gloves (as needed)
1	4	Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall)	Arc-rated face shield or arc flash hood	Arc-rated face shield or safety goggles	Hearing protection (ear canal inserts)
2	8	Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall)	Arc-rated face shield or arc flash hood	Arc-rated face shield or safety goggles	Hearing protection (ear canal inserts)
2.5	8	Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall)	Arc-rated face shield or arc flash hood	Arc-rated face shield or safety goggles	Hearing protection (ear canal inserts)
3	25	Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall)	Arc-rated face shield or arc flash hood	Arc-rated face shield or safety goggles	Hearing protection (ear canal inserts)
4	40	Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall)	Arc-rated face shield or arc flash hood	Arc-rated face shield or safety goggles	Hearing protection (ear canal inserts)

Poster

Arc Flash Training Poster

- Highlights the common causes of arc flash and provides safe work practices and personal protection equipment requirements
- Laminated on both sides to stand up to industrial environments
- Full-color printing and eye-catching graphics for optimum visual impact

Catalog #	Description	Size	Price
104571	Arc Flash Poster	18" x 24"	\$27.65

Arc Flash Sign & Label

- Post signs and labels in the work area and near electrical equipment to boost awareness and compliance
- Signs and labels specify the personal protection equipment required for each arc flash hazard category
- Sign: BradyTuff™ B-401 rigid plastic, laminated graphics, sold individually
- Label: Self-sticking B-302 polyester with overlaminates, available in 5 packs

Catalog #	Description	Size	Price
102523	Arc Flash Protection Sign	10" x 14"	\$10.24
102524	Arc Flash Protection Label	3.5" x 5"	\$10.91

Arc Flash Protection

Wear the proper protective gear when working on or near exposed energized electrical parts. For further information, refer to NFPA 70E, Standard For Electrical Safety In The Workplace.

Hazard / Risk Category	Protective Clothing & Equipment FR = Flame Resistant	Min. arc rating (cal/cm²)
0	<ul style="list-style-type: none"> Long-sleeve shirt and long pants (natural fibers) Safety glasses or safety goggles Hearing protection (ear canal inserts) Leather gloves (as needed) 	N/A
1	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves (as needed) Leather work shoes (as needed) 	4
2	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	8
2.5	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	8
3	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	25
4	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	40

*Arc Rating of PPE should correspond with the Hazard Level and Incident Energy per Voltage-rated gloves and other shock protection may also be required when working on exposed energized parts.

BE SAFE! De-energize and lockout equipment before service or maintenance.

Sign

Arc Flash Protection

Wear the proper protective gear when working on or near exposed energized electrical parts. For further information, refer to NFPA 70E, Standard For Electrical Safety In The Workplace.

Hazard Category	Protective Clothing & Equipment FR = Flame Resistant	Min. arc rating (cal/cm²)
0	<ul style="list-style-type: none"> Long-sleeve shirt and long pants (natural fibers) Safety glasses or safety goggles Hearing protection (ear canal inserts) Leather gloves (as needed) 	N/A
1	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves (as needed) Leather work shoes (as needed) 	4
2	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	8
2.5	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	8
3	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	25
4	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	40

*Arc Rating of PPE should correspond with the Hazard Level and Incident Energy per Voltage-rated gloves and other shock protection may also be required when working on exposed energized parts.

BE SAFE! De-energize and lockout equipment before service or maintenance.

Label

Arc Flash Protection

Wear the proper protective gear when working on or near exposed energized electrical parts. For further information, refer to NFPA 70E, Standard For Electrical Safety In The Workplace.

Hazard Category	Protective Clothing & Equipment FR = Flame Resistant	Min. arc rating (cal/cm²)
0	<ul style="list-style-type: none"> Long-sleeve shirt and long pants (natural fibers) Safety glasses or safety goggles Hearing protection (ear canal inserts) Leather gloves (as needed) 	N/A
1	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves (as needed) Leather work shoes (as needed) 	4
2	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	8
2.5	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	8
3	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	25
4	<ul style="list-style-type: none"> Arc-rated long-sleeve shirt and long pants (or Arc-rated coverall) Arc-rated face shield or arc flash hood Arc-rated face shield or safety goggles Hearing protection (ear canal inserts) Leather gloves and leather work shoes 	40

*Arc Rating of PPE should correspond with the Hazard Level and Incident Energy per Voltage-rated gloves and other shock protection may also be required when working on exposed energized parts.

BE SAFE! De-energize and lockout equipment before service or maintenance.

Wallet Card

Energized Electrical Work Permit

WORK ORDER: _____ DATE: _____

EQUIPMENT ID / LOCATION: _____

WORK DESCRIPTION: _____

ARTISAN/TYPE FOR WORKING LINE: _____

HAZARD INFORMATION

VOLTAGE HAZARD VOLTS: _____

FLASH HAZARD CATEGORY: _____

MIN. ARC RATING (CAL/CM²): _____

OTHER HAZARDS: _____

REQUIRED PROTECTIVE EQUIPMENT

COTTON UNDERWEAR FR SHIRT FLASH HOOD SAFETY GLASSES GLOVES _____

T-SHIRT FR PANTS HARD HAT SAFETY GOGGLES SHARP TOOLS _____

LONG SLEEVE SHIRT FR COVERALL ARC FACE SHIELD LEATHER GLOVES _____

LONG PANTS FLASH SUIT EAR PROTECTION LEATHER SHOES _____

PROCEDURES & PRECAUTIONS

SAFE WORK PROCEDURES: _____

MEANS OF RESTRICTING UNAUTHORIZED ACCESS: _____

EMERGENCY RESPONSE INFORMATION: _____

AUTHORIZATION & APPROVAL

* Only the person(s) listed below are authorized to perform the work described in this permit. * No work other than the tasks described may be performed on or near exposed live parts without prior approval. * If the PPE is not worn during the work, the permit shall be voided and the work shall be stopped immediately. * If the work is not performed safely as described in the above procedures, the permit holder shall be held responsible for any resulting injury or death.

NAME: _____ DATE: _____ INITIALS: _____

NAME: _____ DATE: _____ INITIALS: _____

NAME: _____ DATE: _____ INITIALS: _____

NAME: _____ DATE: _____ INITIALS: _____

APPROVED BY:

NAME: _____ DATE: _____ INITIALS: _____

TITLE: _____

NAME: _____ DATE: _____ INITIALS: _____

TITLE: _____

AFTER WORK IS COMPLETE, RETURN THIS FORM TO:

BRADY © 2004 Brady Corporation. All rights reserved. Printed in U.S.A. C-99257

Permit

Arc Flash Wallet Card

- Ensure compliance and safety by providing each employee with their own arc flash wallet card
- Card specifies the personal protection equipment required for each arc flash hazard category
- Made of laminated cardstock, two-sided printing
- Available in 10 packs

Catalog #	Description	Size	Price
102525	Arc Flash Wallet Card	2.1" x 3.4"	\$20.78

Energized Electrical Work Permit

- Meet NFPA 70E 130.1 (A) requirements which mandate the use of a written permit when performing live electrical work
- 2-ply carbonless copy paper
- 25 permits per pack

Catalog #	Description	Size	Price
99287	Electrical Work Permit	8.5" x 11"	\$21.42

www.BradyID.com

Mr. Ouch Labels




- National Electrical Manufacturers Association (NEMA) recommends use of "Mr. Ouch" labels on transformers in public areas
- Meets NEMA Standard and Underwriters Laboratory Performance Standard #969
- Made from B-927 tamper-resistant film

Catalog #	Description	Size	Qty	Price
46347	Mr. Ouch Label	8" x 4½"	1	\$4.14

Write-On Inspection Labels

- Label size: ¾" x 1½"
- Made of durable, write-on polyester material
- Standard package: 364 identical labels



Catalog # 82588 - \$39.45

Catalog # 82587 - \$39.45



Catalog # 82592 - \$39.45

Catalog # 42211 - \$39.45




Voltage Labels

- Orange markers meet ASME (ANSI) Standard ZG3.22

1 Marker Per Card – Marker Size – 2¼" x 9"
 4 Markers Per Card – Marker Size – 1½" x 4½"
 18 Markers Per Card – Marker Size – ½" x 2¼"

Legend	Catalog Number			Price Each
	Style A 1 Marker/ Card	Style B 4 Markers/ Card	Style C 18 Markers/ Card	
120 Volts	44104	44204	44304	\$2.88
120/208 Volts	44159	44259	44359	\$2.88
240 Volts	44110	44210	44310	\$2.88
277/480 Volts	44160	44260	44360	\$2.88
480 Volts	44115	44215	44315	\$2.88
Single Phase	44129	44229	44329	\$2.88
Three Phase	44131	44231	44331	\$2.88



Warning Labels

- High quality vinyl labels call attention to hazards on paperwork, equipment and packages

Catalog #	Description	Size	Qty	Price
60202	Warning Labels	2"	10/pack	\$93.91
60213	Warning Labels	4"	5/pack	\$62.72

Hard Hat Emblems

- Emblems are self-sticking and card-mounted
- 2" diameter, B-946 indoor/outdoor vinyl film
- Four labels per card



45331 - \$2.79

49581 - \$2.79

49554 - \$2.79

B-997 Silver Reflective Hard Hat Stripes

- Stripe size: 1¼" x 5"
- Standard package: 50



Catalog # 95229 - \$55.40



Gauge Marking Labels

- Color code your gauges to easily identify acceptable or dangerous levels.
- Transparent, adhesive polyester label sheets
- Standard Package: one 9" x 10" sheet

Catalog #	Color	Qty	Price
30697	Red	(1) 9"x10" sheet	\$17.12
30698	Green	(1) 9"x10" sheet	\$17.12
30699	Yellow	(1) 9"x10" sheet	\$17.12




Cabinet Label

- Self-adhesive labels are made of laminated polyester
- Labels are sold individually

Catalog #	Description	Size	Qty	Price
60294	Cabinet Label	3½" x 12"	1	\$6.77
60271	Cabinet Label	7" x 24"	1	\$15.85

Machine & Equipment Labels

- Standard package: Five 3½ x 5 Self-sticking polyester labels
- Price is \$10.93



86783

86861

86868



86799

86793



86204

86203



Tag Fasteners

- Three fastener styles available to meet every application need
- Standard package: 100 per package

Catalog #	Description	Price Each
81760	26 Gauge Galvanized Steel Wire, 12" long	\$14.20
81761	Reusable Beaded Ties 8" long	\$55.53
81762	Nylon Fasteners 8" long	\$12.21

Production Status Tags


- Constructed of durable B-853 cardstock
- Size is 3" x 5 3/4" with 3/8" metal grommet
- 100 tags with string fasteners



86779 - \$51.98




86776 - \$51.98




86761 - \$51.98



86745 - \$51.98




86771 - \$51.98




86740 - \$51.98



86757 - \$51.98




86742 - \$51.98




86751 - \$51.98



86750 - \$51.98



86756 - \$51.98



86757 - \$51.98




86781 - \$51.98

Accident Prevention Tags


- Size is 3" x 5 3/4" with 3/8" metal grommet

† Tags have a larger hole without a grommet to accommodate padlocks.


* Tags have a self-adhesive, clear overlaminated flap which is pressed over the face of the tag for permanent protection.




65372 B-851 \$35.68 (25/pk)
*76198 B-851 \$56.14 (25/pk)
†65349 B-851 \$35.68 (25/pk)



65373 B-851 \$35.68 (25/pk)
*76197 B-851 \$56.14 (25/pk)
†65350 B-851 \$35.68 (25/pk)



76168 B-851 \$39.64 (25/pk)
*76193 B-851 \$56.14 (25/pk)
†65348 B-851 \$39.64 (25/pk)



76171 B-851 \$39.64 (25/pk)
*76192 B-851 \$56.14 (25/pk)
†65347 B-851 \$39.64 (25/pk)



Material

- B-851 - Economy Polyester
- B-853 - Cardstock
- B-837 - Heavy Duty Laminated Polyester



86533 B-851 \$15.89 (10/pk)
86643 B-853 \$51.98 (100/pk)



86524 B-851 \$15.89 (10/pk)
86634 B-853 \$51.98 (100/pk)



86403 B-837 \$22.26 (10/pk)



86537 B-851 \$15.89 (10/pk)
86418 B-837 \$22.26 (10/pk)



Inspection & Material Control Tags

- Tags meet OSHA Standard 1910.145 for accident prevention

Material

- B-851 - Economy Polyester
- B-853 - Cardstock
- B-837 - Heavy Duty Laminated Polyester



86624 - \$16.63 (10/pk)
4"x7" B-851 Polyester




86442 - \$22.26 (10/pk)
3"x5 3/4" B-837 Laminated




86446 - \$22.26 (10/pk)
3"x5 3/4" B-837 Laminated



86620 - \$16.63 (10/pk)
4"x7" B-851 Polyester



86437 - \$22.26 (10/pk)
3"x5 3/4" B-837 Laminated




86625 - \$16.63 (10/pk)
4"x7" B-851 Polyester


86611 - \$16.63 (10/pk)
4"x7" B-851 Polyester

86560 - \$15.89 (10/pk)
3"x5 3/4" B-851 Polyester

86675 - \$51.98 (100/pk)
3"x5 3/4" B-853 Cardstock



86441 - \$22.26 (10/pk)
3"x5 3/4" B-837 Laminated



86614 - \$16.63 (10/pk)
4"x7" B-851 Polyester

86666 - \$51.98 (100/pk)
3"x5 3/4" B-853 Cardstock

Self-Laminating Tags

- Constructed of Brady's durable B-851 polyester with a 1 mil polyester overlay
- Size is 3" x 5¾" with 3/8" metal grommet
- 10 tags with nylon fasteners



Catalog # 86456 - \$22.56



Catalog # 86457 - \$22.56



Catalog # 86458 - \$22.56




Catalog # 86459 - \$22.56
Catalog # 86517 - \$24.16



Catalog # 65501 - \$23.11
Catalog # 96222 - \$24.16

Self-Laminating Blank Tags

- 10 mils polyester tags flex and conform easily to cables of any size.
- Clear, self-laminating flap protects writing from water.



Size (H x W)	White	Yellow	Price Each
5" x 2.5"	102016	102017	\$28.80
5" x 3.25"	102009	102010	\$31.88

Standard Package: 1000 Tags.

Cylinder Status Tag

- Clearly inform user of status of cylinder contents
- Available in Cardstock (B-853) or Polyester (B-851)
- Size: 5¾" x 3"



Catalog #	Description	Price Each
17927	Cardstock Tag (B-853) - 100/pkg.	\$50.45

Recharge Maintenance/ Inspection Tags

- B-851 Rigid Polyester
- Size is 3" x 5¾" with 3/8" metal grommet
- Standard package: 25 tags includes plastic lock-on ties




Catalog # 76222 - \$39.64

Catalog # 65371 - \$39.64

Aluminum Write-On Tags


- B-184 Dead Soft Aluminum Foil laminated to a cardboard backing
- Long-lasting indoor performance for handwritten or typed images (Not intended for outdoor use)
- Standard package: 25 write-on tags (includes plastic lock-on ties)



Catalog #	Description	Qty	Price
23199	Aluminum Write-On Tags	25	\$34.98

Scaffolding Tags

- B-837 plastic and B-851 polyester tags withstand moisture, grease and dirt. Sold 10 per package and include nylon fasteners.
- B-853 card stock are sold 100 per package and includes string fasteners
- Tags feature two chamfered corners and a 3/8" grommeted hole



Heavy Duty Laminated Tag (B-837)	"OK" Green Tag	"Danger" Red Tag	"Caution" Yellow Tag	Price
5¾" x 3"	86452	86453	-	\$22.26
Economy Polyester (B-851)				Price
5¾" x 3"	86572	86573	86574	\$15.89
Cardstock Tags (B-853)				Price
5¾" x 3"	86682	-	86684	\$51.98

Scaffold Status Holder & Tag

- .060" thick plastic tag with clear front pocket
- Size: 12" x 4½" - accommodates tags with a size of 5¾" x 3"

Catalog #	Description	Price
48111	Holder Only	\$26.94
48112	Holder Kit (holder + 3 tags)	\$36.19

Scaffolding Tags

- SCAFFTAG® provides system, procedural and legal compliance
- Provides a clear inspection trail giving integrity and control of work carried out
- Essential for companies working with ISO9000 clients



Catalog #	Description	Qty.	Color	Size	Price
104111	Holders	10/Box	White	11 3/4" x 3 1/2"	\$68.36
104112	Holders	10/Box	Red	11 3/4" x 3 1/2"	\$68.36
104113	Inspection Inserts	100/Pkg	Green	3 3/4" x 7 5/8"	\$162.75
104114	Caution Inserts	100/Pkg	Yellow	3 3/4" x 7 5/8"	\$162.75
104115	Standard Kit*	1/Kit	White		\$119.63
104116	Scafftag II Holder	10/Box	White	11 1/2" x 6"	\$101.68
104117	Inspection Inserts	100/Pkg	Green	5 3/4" x 7 5/8"	\$183.75
104118	Scafftag II Kit*	1/Kit			\$153.80

*Kits include 10 Holders, 20 Inserts and 1 Pen

Micro Tag

A safety system which is particularly useful for identifying small plant, equipment, lifting gear and safety harnesses. Color coded and date qualified, the system also has the facility to render equipment in a 'prohibition status' should it be found to be faulty between inspection dates. Meets the requirements for OSHA CFR 1926.502 (d) (21) Personal Fall Arrest systems.



Cat No.	Description	Qty.	Color	Size	Price
104152	Next Inspection Date Due	100	Green	1 7/8" x 1 3/4"	\$81.38
104155	Next Inspection Date Due	100	Red	1 7/8" x 1 3/4"	\$81.38
104157	Next Inspection Date Due	100	Yellow	1 7/8" x 1 3/4"	\$81.38
104143	Microtag Kit*	1			\$68.36

*Kit includes 20 holders, 40 cables ties and 1 pen

MultiTag®

Assists with the identification and preventative maintenance requirements of a range of equipment, and may assist with the requirements of CFR 1926.1053 (a) (12), (b) (17) (i) (ii) and CFR 1910.25 (d) (1) (X) US Patent # 314,016



Catalog #	Description	Qty./UOM	Color	Size	Price
104122	Multitag Holder	10/BOX	White	2 3/4" x 8 3/4"	\$68.36
104123	Multitag Inserts	100/PK	Green	2" x 6 1/2"	\$162.75
104124	Multitag Kit	1/KIT			\$95.70

*Kit includes 10 holders, 10 inserts and 1 pen

LadderTags™

LADDERTAG™ is a complete ladder safety management system. Regulations require ladders to be checked for damage, faults and wear before use by an authorized user, and may assist with the requirements of CFR 1926.1053 (a) (12), (b) (17) (i) (ii) and CFR 1910.25 (d) (1) (X)



Catalog #	Desc.	Qty.	Color	Size	Price
104125	Holder	10/BOX	White	2 3/4" x 8 3/4"	\$68.36
104126	Inserts	100/PK	Yellow	2" x 6 1/2"	\$162.75
104127	Kit*	1/KIT			\$95.70

*Kit includes 10 holders, 10 inserts and 1 pen

Forklift™ Tag

Assists with the requirements of 1910.178 (q) (7) pre use preventative maintenance and safety inspection for forklift trucks. The FORKLIFT™ holder is permanently attached to the cage of the forklift truck and displays the prohibition sign and the script "DO NOT USE". The FORKLIFT™ insert shows in written and graphic format the daily or pre-shift, inspections to be carried out by the first user.



Catalog #	Description	Qty./UOM	Color	Size	Price
104128	Forklift Holder	10/BOX	White	11 1/2" x 6"	\$55.13
104129	Forklift Inserts	100/PK	Blue/Yellow	5 3/4" x 7 5/8"	\$284.81
104130	Forklift Kit*	1/KIT			\$126.46

*Kit includes 10 holders, 10 status inserts and 1 pen

EntryTag®

Works in conjunction with existing permit to work systems and assist with the requirements of CFR 1910.146 (c) (2), (d) (11) and (f) (2). ENTRYTAG® is a visual reminder to authorized personnel and assists in instructing non authorized personnel of the critical requirements contained within the permit to work. The system clearly states the minimum requirements of entry to the confined space or whether the area is in prohibition and cannot be entered.



Catalog #	Description	Qty./UOM	Color	Size	Price
104119	Entrytag Holder	10/BOX	White	11 3/4" x 6"	\$85.45
104120	Standard Inserts	100/PK	Green	5 3/4" x 7 5/8"	\$284.81
107967	Man In Tank Tag	100/PK	Yellow	2" x 6 1/2"	\$162.75
104121	Entry Tag Kit*	1/KIT			\$126.46

*Kit includes 10 holders, 20 inserts and 1 pen

Valve Tags

www.BradyID.com

Valve Tags

ASME A13.1

Recommends the use of a permanently legible tag for identification of materials in pipes less than 3/4" (19mm) in diameter.



Durable Plastic Tags (B-418)

- Durable Plastic Tags are lightweight, non-corrosive, non-conductive and impact resistant
- Tag withstands temperatures between -40°F to 260°F
- Rounded corners and hole punched
- Tags are sold individually

Color	Catalog Number	
	3"x1½"	4"x2½"
White	87696	87697
Orange	87694	87695
Red	41924	41925
Yellow	41922	41923
Black	41920	41921
Blue	41926	41927
Brown	87710	87711
Tan	87712	87713
Grey	87698	87699
Green	41928	41929



Blank Stainless Steel Tags (B-919)

- Ideal for harsh environments or where a stainless steel material is specified
- Tag hole is 3/16"
- Standard package: 25 tags

Catalog Number	Tag Size	Tag Shape	Price
44400	1½"	Round	\$45.05
44401	1½"	Square	\$45.05
44402	2"	Round	\$58.79
44403	2"	Square	\$58.79



Blank Aluminum Tags (B-906)

- Anodized aluminum is dyed to offer color-coding options not available with brass tags
- Available in twelve colors
- Choose from 1½" or 2" round styles
- Standard package: 25 tags

Color	2" Round	2" Square	1½" Round	1½" Square
Black	87612	87637	87605	87619
Blue	49907	87641	49902	87629
Gold	87608	87633	87601	87615
Green	49908	87642	49903	87630
Light Blue	87613	87638	87606	87620
Natural	49909	87643	49904	87631
Olive Drab	87609	87634	87602	87616
Orange	87611	87636	87604	87618
Pink	87610	87635	87603	87617
Red	49906	87640	49901	87628
Violet	87607	87632	87600	87614
Yellow	49905	87639	49900	87627



Stamped Brass Valve Tags (B-907)

- 19 gauge cartridge brass (40 mils thick)
- 1½" diameter
- Standard package: 25 identical tags

Catalog Number	Bottom Line Number Sequence	Price
23200	1 - 25	\$35.60
23201	26 - 50	\$35.60
23202	51 - 75	\$35.60
23203	76 - 100	\$35.60



Blank Brass Valve Tags (B-907)

- Standard package: 25 identical tags
- Customize your own brass tags with Brady steel stamps

Catalog #	Description	Price
23210	1½" Round	\$14.04
23211	2" Round	\$16.12
23212	1½" Square	\$16.12
23213	2" Square	\$24.22



Valve Chart Frames

- Use Valve Chart Frames to display your valve tag charts
- Use valve tag chart to list up to 50 locations
- Rugged extruded, clear anodized aluminum frame comes with clear plastic window
- Frame holds 8" x 11" valve tag charts

Catalog No.	Description	Price
23309	Valve Chart Frame	\$32.90

NEW!

Print your own heavy-duty valve tags with the new **BBP®31 Sign & Label Printer.**

View page 136 for more information.





Solid "S" Hooks

- Standard package: 100 "S" Hooks, sold in full packages only

Catalog Number	Material	Size	For Valve Stems		Price
			Up To		
23305	Brass	1 3/4" O.D.	1/2"		\$32.98
23304	Brass	1 1/2" O.D.	3/8"		\$32.49
23303	Brass	1 1/4" O.D.	1/4"		\$30.77



Lead Seals

- 12" wires with pre-fitted lead seals fit easily around pipes or valves
- Use with Hand Sealing Press
- Standard package: 250

Catalog #	Description	Price
23301	Copper Lead Seals	\$57.18



#16 Jack Chain

- Approximately 25 links per foot
- Standard package: 50 feet of chain, sold in full packages only

Catalog Number	Description	Price
23308	Brass #16	\$44.94
98859	Stainless Steel	\$43.61



Zinc Wire Clamps - Double Ferrule Design

- Use to secure or splice Stainless Steel Wire
- Standard package: 50

Catalog #	Description	Price
38090	Zinc Wire Clamps	\$17.43



4 1/2" Beaded Chain

- Standard package: 100 chains, sold in full packages only

Catalog Number	Description	Price
23306	#6 Brass	\$21.61



Stainless Wire (48 mil)

- 30' rolls

Catalog #	Description	Price
38091	Stainless Steel Wire (48 mil)	\$12.81

NEW!

Create Custom Valve Tags Online

Design your facility's Valve Tags with this easy-to-use design tool. Enter multiple lines of custom text, and choose from a variety of styles, sizes and materials.

- Choose Stamped or Engraved
- Up to 5 Material Choices
- Color and Numbering Options Available

Try the Custom Design Tool at www.BradyID.com!

Easy as 1, 2, 3!

- 1) Select your category
- 2) Customize your product
- 3) Add to your shopping cart



Create custom products in minutes!

Ships in 24-48 hours!

ASME Standard For Pipe Identification

www.BradyID.com/pipemarkers

ASME (ANSI) Standard A13.1-2007

The ASME (ANSI) Standard for pipe identification is a widely used guideline in determining pipe identification requirements. The purpose of the standard is to "assist in identification of hazardous materials conveyed in piping systems and their hazards when released into the environment."
 "Pipes are defined as conduits for the transport of gases, liquids, semi-liquids or fine particulate dust."

Brady Pipe Marking Systems Meet the ASME (ANSI) A13.1-2007 Standard

The Brady Pipe Marking System instantly tells you all you need to know...
 pipe contents...direction of flow...whether hazardous or safe.

Brady Pipe Marking Systems Meet the ASME (ANSI) Size Recommendations

The A13.1-2007 standard also makes recommendations as to the size of letter height and length of color field for various pipe diameters. These recommendations are shown in the table.

Outside Diameter of Pipe or Covering	Size of Letters
3/4" to 1 1/4"	1/2"
1 1/2" to 2"	3/4"
2 1/2" to 6"	1 1/4"
8" to 10"	2 1/2"
Over 10"	3 1/2"

NOTE: For pipes less than 3/4" in diameter, a permanently legible tag is recommended.

Brady Pipe Marking Systems Meet ASME (ANSI) Color Recommendations



Unmarked pipes mean danger – to both life and property. Numerous injuries have occurred through ignorance of pipe contents, particularly when outside agencies are called in under emergency conditions.

Classification	Color Scheme
Fire Quenching Fluids	White on Red
Toxic & Corrosive Fluids	Black on Orange
Flammable Fluids	Black on Yellow
Combustible Fluids	White on Brown
Potables, cooling, boiler feed and other water	White on Green
Compressed Air	White on Blue

Brady Pipe Marking Systems Meet the ASME (ANSI) A13.1-2007 Standard Visibility

"Markers shall be located so that they are readily visible to plant personnel from the point of normal approach." Brady Pipe Markers instantly tell you all you need to know about pipe contents, direction of flow and whether hazardous or safe.

Brady Recommendations for Marker Placement:



NEW!

Online Custom Design Tool

Design AMSE (ANSI) compliant Pipe Markers that meet the exact specification of your facility's pipes. Choose your style, size, color and custom text.

Try the Custom Design Tool at www.BradyID.com!

Easy as 1, 2, 3!

- 1) Select your category
- 2) Customize your product
- 3) Add to your shopping cart



Create custom products in minutes!
 Ships in 24-48 hours!

Pipe Marker Material Selection

www.BradyID.com/pipemarkers

Use the chart below to help determine which material best meets your pipe marker application needs.

Characteristic	HARSH ENVIRONMENT		PURPOSE		
	Mechanically Applied		Mechanically Applied	Self-Sticking	
	Wrap-Around Polyester B-689	High Performance High Visibility B-681/B-883	B-915 Brady Snap-On™ and Strap-On Vinyl	Self-Sticking Vinyl B-946	Self-Sticking Plastic Film B-736
PLANT ENVIRONMENT					
Indoor	Good	Good	Good	Good	Good
Avg. Outdoor Durability (yrs.)	5-8	5-8	5-8	3-5	2-3
Surface Abrasion Resistance	Good	Good	NR	NR	NR
TEMPERATURE					
Min. Installation Temperature	40°F, 5°C	—	—	0°F, -18°C	50°F, 10°C
Upper Temperature Limit	248°F, 120°C	230°F, 110°C	180°F, 82°C	180°F, 82°C	212°F, 100°C
Lower Temperature Limit	-40°F, -40°C	-40°F, -40°C	-40°F, -40°C	-40°F, -40°C	-40°F, -40°C
PIPE SURFACE					
Dirty, Dusty	Good	Good	Good	NR	NR
Rough	Good	Good	Good	Good	NR
Insulated	Good	Good	Good	Good	Good
Wet	Good	Good	Good	NR	NR
Greasy, Oily	Good	Good	Good	NR	NR
CHEMICAL RESISTANCE					
Organic Solvents (MEK, Acetone, Toluene)	NR	NR	NR	NR	NR
Acids (Sulfuric, HCL, Acetic)t	Good	Good	NR	NR	Good
Alkalis (Sodium Hydroxide)	Good	Good	NR	NR	NR
Alcohols (Methanol, Isopropanol)	Good	Good	Good	Good	Good
Grease/Oils (SAE 20, ASTM #3)	Good	Good	Good	Good	Good
SPECIAL PROPERTIES					
Low PVC					
Pipe contact point	Yes	Yes	No	No	No
Whole marker	No	Yes	No	No	No
Low Halogen					
Pipe contact point	Yes	Yes	No	No	No
Whole marker	No	Yes	No	No	No
Meets ASME (ANSI) A13.1	Yes	Yes	Yes	Yes	Yes

n/a = data not available

NR = marker not recommended for environment listed

Good = marker suitable for environment listed

Self-Sticking Vinyl Pipe Markers


www.BradyID.com/pipemarkers



Self-Sticking Vinyl Pipe Markers

- Markers meet the requirements of the ASME (ANSI) A13.1 Standard for the identification of piping system contents when used with Directional Flow Arrow Tape
- Markers supplied on a coated backing material that makes handling and installation easy
- Marker ends should be banded with Brady Directional Flow Arrow Tape to indicate pipe content flow direction
- Durable B-946 material ideal for indoor and outdoor environments

Size Chart

Outside Diameter	Letter Height	Style Description	Order Style*	Price
8" or greater	3½"	HEATING RETURN Style 1HV: One 4" x 24" marker per card	1HV	\$4.74
2½" to 7½"	2"	HEATING RETURN Style 1: One 2¼" x 14" marker per card	1	\$2.33
¾" to 2¾"	¾"	FIRE AUTO SPRINKLERS FIRE AUTO SPRINKLERS FIRE AUTO SPRINKLERS FIRE AUTO SPRINKLERS Style 4: Four 1½" x 7" markers per card	4	\$2.33
less than ¾"	½"	 Style 3C: Three 2¼" x 2¾" markers per card plus 8 strips of Arrow Tape	3C	\$2.33

! Customize Pipe Markers Online

Create custom pipe markers quickly and easily using the Custom Design Tool online! Visit www.BradyID.com

*When ordering, please indicate the catalog number for your desired legend followed by the Order Style (1HV, 1, 4 or 3C) that corresponds with your desired size and style. (Example: Air = 7005-3C)

Legend	Background Color	Catalog No.	Legend	Background Color	Catalog No.	Legend	Background Color	Catalog No.
AIR	Yellow	7005 -*	DOMESTIC HOT	Yellow	7088 -*	NON-POTABLE WATER	Yellow	7203 -*
AIR	Blue	7006 -*	WATER RETURN	Yellow	7088 -*	OVERFLOW	Yellow	7208 -*
AIR	Green	7007 -*	DOMESTIC HOT	Yellow	7089 -*	OXYGEN	Green	7210 -*
AIR SUPPLY	Blue	7010 -*	WATER SUPPLY	Yellow	7090 -*	OXYGEN	Yellow	7209 -*
ARMONIA	Yellow	7014 -*	DRAIN	Green	7107 -*	PLANT AIR	Yellow	7212 -*
ARGON	Green	7015 -*	FIRE AUTO SPRINKLERS	Red	7110 -*	POTABLE WATER	Yellow	7218 -*
ASBESTOS FREE	Blue	7017 -*	FIRE PROTECTION WATER	Red	7110 -*	PROCESS WATER	Green	7224 -*
ASBESTOS FREE INSULATION	Blue	7018 -*	FUEL OIL	Yellow	7115 -*	PROPANE GAS	Yellow	7227 -*
ASBESTOS INSULATION	Yellow	7019 -*	GAS	Yellow	7119 -*	RAIN WATER	Green	7229 -*
BLANK	Yellow	7025 -*	GLYCOL	Yellow	7121 -*	REFRIGERANT LIQUID	Yellow	7235 -*
CHILLED WATER	Green	7045 -*	GLYCOL RETURN	Yellow	7122 -*	RETURN	Green	7242 -*
CHILLED WATER RETURN	Green	7046 -*	GLYCOL SUPPLY	Yellow	7123 -*	RETURN	Yellow	7244 -*
CHILLED WATER SUPPLY	Green	7047 -*	HEATING RETURN	Yellow	7125 -*	ROOF DRAIN	Green	7247 -*
CITY WATER	Green	7054 -*	HEATING SUPPLY	Yellow	7127 -*	SANITARY SEWER	Green	7250 -*
COLD WATER	Green	7055 -*	HEATING WATER	Yellow	7128 -*	SANITARY SEWER	Yellow	7251 -*
COMPRESSED AIR	Yellow	7058 -*	HEATING WATER RETURN	Yellow	7129 -*	SANITARY VENT	Yellow	7252 -*
COMPRESSED AIR	Green	7059 -*	HEATING WATER SUPPLY	Yellow	7130 -*	SANITARY WASTE	Yellow	7253 -*
COMPRESSED AIR	Blue	7060 -*	HIGH PRESSURE	Yellow	7137 -*	SPRINKLER	Red	7267 -*
CONDENSATE	Yellow	7061 -*	CONDENSATE	Yellow	7146 -*	SPRINKLER FIRE	Red	7268 -*
CONDENSATE DRAIN	Yellow	7062 -*	HOT WATER	Yellow	7146 -*	SPRINKLER WATER	Red	7269 -*
CONDENSATE DRAIN	Green	7063 -*	HOT WATER	Yellow	7147 -*	STEAM	Yellow	7270 -*
CONDENSATE RETURN	Yellow	7065 -*	RECIRCULATION	Yellow	7147 -*	STORM DRAIN	Green	7273 -*
CONDENSER WATER	Green	7067 -*	HOT WATER RETURN	Yellow	7148 -*	STORM SEWER	Green	7274 -*
CONDENSER	Green	7068 -*	HOT WATER SUPPLY	Yellow	7149 -*	SUPPLY	Green	7282 -*
WATER RETURN	Green	7068 -*	INDUSTRIAL WATER	Green	7163 -*	SUPPLY	Yellow	7311 -*
CONDENSER	Green	7069 -*	LOW PRESSURE	Yellow	7175 -*	TEMPERED WATER	Yellow	7283 -*
WATER SUPPLY	Green	7069 -*	CONDENSATE	Yellow	7175 -*	TOWER WATER	Green	7285 -*
COOLING WATER	Green	7070 -*	LOW PRESSURE STEAM	Yellow	7179 -*	VACUUM	Yellow	7291 -*
COOLING WATER RETURN	Green	7071 -*	MEDICAL AIR	Yellow	7184 -*	VACUUM	Green	7292 -*
DEIONIZED WATER	Green	7073 -*	MEDICAL AIR	White	7186 -*	VENT	Yellow	7295 -*
DOMESTIC COLD WATER	Green	7084 -*	MEDICAL VACUUM	White	7186 -*	VENT	Green	7296 -*
DOMESTIC COLD	Green	7084 -*	MEDIUM PRESSURE	Yellow	7190 -*	WASTE	Yellow	7298 -*
WATER SUPPLY	Green	7086 -*	NATURAL GAS	Yellow	7196 -*	WASTE	Green	7299 -*
DOMESTIC HOT WATER	Yellow	7087 -*	NATURAL GAS	Yellow	7196 -*	WATER	Yellow	7303 -*
			NITROGEN	Green	7198 -*	WATER	Green	7304 -*
			NITROGEN	Blue	7200 -*			

Spanish Legends

Legend	Background Color	1HV	1	4	3C	Legend	Background Color	1HV	1	4	3C
AGUA	Green	83596	83540	83576	83615	DESAGUE SANITARIO	Green	83589	83527	83563	
AGUA DE REFRIGERACION	Green	83484	83424	83460		GAS	Yellow	83489	83432	83468	83501
AGUA FRIA	Green	83418	83418	83453	83498	GAS NATURAL	Yellow	83585	83517	83553	83601
AGUA POTABLE	Yellow		83522	83558		HIDROGENO	Yellow		83510	83545	83598
AGUA REFRIGERADA	Green	83477	83414	83449		OXIGENO	Green		83520	83556	83604
AGUA PROTEC. PAPA INCENDIOS	Red		83430	83466		RESPIRADERO	Yellow		83537	83573	83612
AIRE	Blue		83400	83436		RETORNO DE AGUA REFRIGERADA	Green	83478	83415	83450	
AIRE COMPRIMIDO	Blue		83421	83456	83501	SUMINISTRO AGUA REFRIGERADA	Green	83479	83416	83451	
AIRE USO MEDICO	Yellow		83514	83550	83599	VACIO USO MEDICO	White		83515	83551	83600
CAUSTICA	Yellow		83413	83448	83496	VAPOR	Yellow	83590	83530	83566	83607

Snap-On & Strap-On Pipe Markers

www.BradyID.com/pipemarkers



BradySnap-On™ Vinyl Pipe Markers are designed for general purpose pipe identification on pipes that have an outside diameter between ¾" and 6".



Strap-On Pipe Markers are designed for general purpose pipe identification on pipes that have a 6" or larger diameter.

BradySnap-On™ & Strap-On Pipe Markers

- Designed for pipes that have an outside diameter between ¾" and 6" (including insulation)
- May be applied to dirty, oily, greasy or rough surfaces
- All stock BradySnap-On™ Strap-On Markers meet ASME (ANSI) Standard
- Strap-On Supplied as a flat sheet with slots to accommodate BradyLock™ Fastener straps. Styles F - H come with nylon straps

Pipe Markers

BradySnap-On™ Markers Size Chart

Outside Diameter	Letter Height	Style Description*	Price
¾" to 1¾"	½"	Style A	\$4.63
1½" to 2¾"	¾"	Style B	\$6.38
2½" to 3½"	1¼"	Style C	\$11.79
4" to 6"	1¾"	Style D	\$12.62

Strap-On Style Marker Size Chart

Outside Diameter	Letter Height	Style Description	Price
6" to 7½"	1¼"	Style F	\$13.04
8" to 9½"	2½"	Style G	\$18.50
10" to 15"	3½"	Style H	\$23.29

*When ordering, please indicate the catalog number for your desired legend followed by the letter code (A-D, F-H) that corresponds with your desired size and style. (Example: Air = 4001-H)

Legend	Background Color	Catalog No.	Legend	Background Color	Catalog No.	Legend	Background Color	Catalog No.
AIR	Green	4001 - *	DRAIN	Green	4055 - *	NON-POTABLE WATER	Yellow	4102 - *
AIR	Blue	4002 - *	FIRE AUTO SPRINKLERS	Red	4059 - *	OIL	Yellow	4103 - *
AIR	Yellow	4003 - *	FIRE MAIN	Red	4185 - *	OXYGEN	Yellow	4105 - *
ARGON	Blue	4162 - *	FIRE PROTECTION WATER	Red	4060 - *	OXYGEN	Green	4106 - *
ARGON	Green	4006 - *	FUEL OIL RETURN	Yellow	4064 - *	OXYGEN	Blue	4107 - *
ASBESTOS FREE	Blue	4007 - *	FUEL OIL SUPPLY	Yellow	4065 - *	PLANT AIR	Yellow	4108 - *
(BLANK)	Yellow	4010-A	GAS	Yellow	4067 - *	PLUMBING VENT	Green	4110 - *
(BLANK)	Red	4012-A	HEATING RETURN	Yellow	4070 - *	POTABLE WATER	Green	4111 - *
CARBON DIOXIDE	Yellow	4019 - *	HEATING SUPPLY	Yellow	4071 - *	PROCESS WATER	Green	4113 - *
CAUSTIC	Yellow	4020 - *	HEATING WATER RETURN	Yellow	4072 - *	PROPANE GAS	Yellow	4114 - *
CHILLED WATER	Green	4022 - *	HEATING WATER SUPPLY	Yellow	4073 - *	RETURN	Yellow	4119 - *
CHILLED WATER RETURN	Green	4023 - *	HELIUM	Green	4074 - *	ROOF DRAIN	Green	4121 - *
CHILLED WATER SUPPLY	Green	4024 - *	HIGH PRESSURE AIR	Yellow	4075 - *	SANITARY DRAIN	Green	4122 - *
CITY WATER	Green	4028 - *	HIGH PRESSURE CONDENSATE	Yellow	4076 - *	SANITARY SEWER	Green	4123 - *
COLD WATER	Green	4029 - *	HIGH PRESSURE STEAM	Yellow	4077 - *	SERVICE WATER	Green	4270 - *
COMPRESSED AIR	Yellow	4032 - *	HIGH PRESSURE WATER	Yellow	4078 - *	SODIUM HYPOCHLORITE	Yellow	4124 - *
COMPRESSED AIR	Green	4033 - *	HOT	Yellow	4197 - *	SPRINKLER FIRE	Red	4127 - *
COMPRESSED AIR	Blue	4034 - *	HOT WATER	Yellow	4079 - *	SPRINKLER WATER	Red	4128 - *
CONDENSATE	Yellow	4035 - *	HOT WATER RETURN	Yellow	4081 - *	STEAM	Yellow	4129 - *
CONDENSATE DRAIN	Yellow	4036 - *	HOT WATER SUPPLY	Yellow	4082 - *	STORM DRAIN	Green	4132 - *
CONDENSATE RETURN	Yellow	4037 - *	HYDRAULIC LINE	Yellow	4083 - *	STORM WATER	Green	4134 - *
COOLING WATER RETURN	Green	4043 - *	HYDRAULIC OIL	Yellow	4199 - *	SULFURIC ACID	Yellow	4136 - *
COOLING WATER SUPPLY	Green	4044 - *	HYDROCHLORIC ACID	Yellow	4085 - *	TEMPERED WATER	Yellow	4140 - *
DEIONIZED WATER	Green	4046 - *	HYDROGEN	Yellow	4086 - *	TOWER WATER RETURN	Green	4143 - *
DEIONIZED WATER RETURN	Green	4172 - *	INSTRUMENT AIR	Blue	4089 - *	VACUUM	Yellow	4146 - *
DEIONIZED WATER SUPPLY	Green	4173 - *	LAB VENT	Yellow	4225 - *	VACUUM	Green	4147 - *
DOMESTIC COLD WATER	Green	4048 - *	LAB WASTE	Yellow	4226 - *	VENT	Yellow	4148 - *
DOMESTIC COLD WATER SUPPLY	Green	4050 - *	LOW PRESSURE CONDENSATE	Yellow	4091 - *	VENT	Green	4150 - *
DOMESTIC HOT WATER	Yellow	4051 - *	LOW PRESSURE STEAM	Yellow	4092 - *	WASTE	Yellow	4151 - *
DOMESTIC HOT WATER RETURN	Yellow	4052 - *	NATURAL GAS	Yellow	4097 - *	WASTE WATER	Yellow	4152 - *
DOMESTIC HOT WATER SUPPLY	Yellow	4053 - *	NITRIC ACID	Yellow	4247 - *	WASTE WATER	Green	4153 - *
			NITROGEN	Yellow	4098 - *	WATER	Green	4155 - *
			NITROGEN	Green	4099 - *			
			NITROGEN	Blue	4100 - *			

NEW!

BBP®31 Sign & Label Printer

Make your own custom pipe markers for up to 70% less! The BBP®31 Sign & Label Printer can take on all the different labeling needs of your facility - including your pipe marking needs!

View page 132 for more informations or visit www.BradyID.com/bbp31



High Performance Pipe Markers

www.BradyID.com/pipemarkers

B-689 High Performance Pipe Markers

- PVF overlaminated polyester construction seals in and protects graphics
- Markers resist abrasion, chemicals, high humidity and outdoor weathering
- Ideal for pipes up to 7 7/8" in diameter
- Choose from more than 125 stock legends or create your own custom legend



B-689 High Performance Pipe Markers are pre-coiled for easy wrap-around installation on pipe up to 7 7/8" in diameter.

Size Chart

Outside Diameter	Max. Char. Per Marker	Letter Height	Style Description*	Price
Coiled Wrap-Around				
1/2" to 1 3/8"	22	1/2"	Style O	\$7.39
1 1/2" to 2 3/8"	13	3/4"	Style I	\$9.59
2 1/2" to 7 7/8"	13	1 1/4"	Style II	\$13.57

*When ordering, please indicate the catalog number for your desired legend followed by the letter code (O, I, II, or HPHV) that corresponds with your desired size and style. (Example: Air = 7005-3C)

Legend	Background Color	Catalog No.	Legend	Background Color	Catalog No.	Legend	Background Color	Catalog No.
(BLANK LABEL)	Blue	5600 - *	DOMESTIC HOT WATER RETURN	Yellow	5676 - *	NITROGEN	Green	5728 - *
(BLANK LABEL)	Green	5601 - *	DRAIN	Green	5678 - *	NITROGEN	Yellow	5729 - *
(BLANK LABEL)	Red	5602 - *	DRAIN	Yellow	5679 - *	NON-POTABLE WATER	Yellow	5730 - *
(BLANK LABEL)	Yellow	5603 - *	FIRE PROTECTION	Red	5688 - *	OXYGEN	Yellow	5736 - *
60# STEAM	Yellow	5609 - *	FIRE PROTECTION WATER	Red	5689 - *	PLANT AIR	Yellow	5738 - *
150# STEAM	Yellow	5614 - *	FLOOR DRAIN	Yellow	5690 - *	PLANT WATER	Green	5739 - *
AIR	Blue	5625 - *	FOUL CONDENSATE	Yellow	5691 - *	POTABLE WATER	Green	5744 - *
ANHYDROUS AMMONIA	Yellow	5631 - *	#6 FUEL OIL	Yellow	5694 - *	PROCESS WATER	Yellow	5746 - *
BLACK LIQUOR	Yellow	5634 - *	FUEL OIL	Yellow	5695 - *	PROCESS WATER	Green	5747 - *
BOILER BLOWDOWN	Yellow	5636 - *	FUEL OIL RETURN	Yellow	5696 - *	RAW WATER	Green	5750 - *
BOILER FEED WATER	Yellow	5637 - *	FUEL OIL SUPPLY	Yellow	5697 - *	ROOF DRAIN	Green	5754 - *
CAUSTIC	Yellow	5643 - *	GREEN LIQUOR	Yellow	5699 - *	SANITARY SEWER	Yellow	5755 - *
CHEMICAL FEED	Yellow	5645 - *	HEATING SUPPLY	Yellow	5701 - *	SEAL WATER	Green	5758 - *
CHILLED WATER	Green	5646 - *	HEATING WATER RETURN	Yellow	5702 - *	SODIUM HYPOCHLORITE	Yellow	5761 - *
CHILLED WATER RETURN	Green	5647 - *	HEATING WATER SUPPLY	Yellow	5703 - *	SPRINKLER WATER	Red	5765 - *
CHILLED WATER SUPPLY	Green	5648 - *	HIGH PRESSURE STEAM	Yellow	5706 - *	STEAM	Yellow	5767 - *
CITY WATER	Green	5655 - *	HOT WATER	Yellow	5707 - *	STORM DRAIN	Green	5769 - *
COMPRESSED AIR	Blue	5660 - *	HYDRAULIC OIL	Yellow	5711 - *	SULFURIC ACID	Yellow	5774 - *
COMPRESSED AIR	Yellow	5661 - *	INSTRUMENT AIR	Blue	5716 - *	TURPENTINE	Yellow	5776 - *
CONDENSATE	Yellow	5662 - *	LOW PRESSURE CONDENSATE	Yellow	5719 - *	VACUUM	Green	5777 - *
CONDENSATE DRAIN	Green	5663 - *	LOW PRESSURE STEAM	Yellow	5720 - *	VENT	Green	5780 - *
CONDENSATE RETURN	Yellow	5664 - *	MAKE-UP WATER	Green	5722 - *	VENT	Yellow	5781 - *
CONDENSER WATER RETURN	Green	5665 - *	MEDIUM PRESSURE STEAM	Yellow	5723 - *	WARM MILL WATER	Green	5782 - *
COOLING WATER	Green	5668 - *	MILL AIR	Blue	5724 - *	WASTE WATER	Yellow	5784 - *
DEMIN. WATER	Green	5672 - *	MILL WATER	Green	5725 - *	WATER	Green	5786 - *
DOMESTIC COLD WATER	Green	5673 - *	NATURAL GAS	Yellow	5726 - *	WATER	Yellow	5787 - *
DOMESTIC HOT WATER	Yellow	5675 - *	NITRIC ACID	Yellow	5727 - *	Well Water	Green	5790 - *



OSHA Federal Regulation 29 CFR 1910.261

"Pulp, Paper and Paperboard Mills"

This regulation applies to plants where pulp, paper and paperboard are converted. "All chlorine, caustic and acid lines shall be marked for positive identification in accordance with ASME (ANSI) Standard A13.1.





Snap-On Cable Markers

- Fits on 1/2 diameter cables
- Pre-coiled for easy installation
- Use on dusty, dirty, oily or scaly pipe surfaces
- Printed on durable vinyl
- Outdoor durability from 5 to 8 years

Legend	Catalog Number	Bkgnd/ Legend	Length of Color Field	Price
Caution Fiber Optic Cable	47659	Orange/Black	5"	\$4.86



Directional Flow Arrow Tape

- Durable B-946 material withstands the elements indoors or out
- Provides 360° visibility
- Supplied in liner-mounted rolled form - use two bands per marker

Roll Size	Blk/Ylw	Wht/Grn	Wht/Rd	Price Each
1" x 30 yds	91424	91425	91426	\$27.07
2" x 30 yds	91420	91421	91422	\$54.07
4" x 30 yds	91287	91290	91288	\$108.11

Roll Size	Blk/Grn	Blk/Org	Blk/Gray	Price Each
1" x 30 yds	91412	-	-	\$27.07
2" x 30 yds	91416	91418	91419	\$54.07
4" x 30 yds	-	91410	-	\$108.11

Roll Size	Wht/Blu	Blk/Wht	Price Each
1" x 30 yds	91427	91413	\$27.07
2" x 30 yds	91423	91417	\$54.07
4" x 30 yds	91289	91409	\$108.11



Solid Color Pipe Banding Tape

- Durable B-946 material withstands the elements indoors or out
- Meets ASME color field size recommendation when used in combination with worded legends and directional flow arrows
- Supplied in liner-mounted rolled form
- Use two bands per marker

Roll Size	Yellow	Green	Red	Orange	Price Each
1" x 30 yds	36301	36304	36302	91428	\$21.79
2" x 30 yds	55260	55263	55261	91430	\$43.58
4" x 30 yds	36287	36290	-	-	\$87.13

Roll Size	Blue	Brown	Blk	Gray	Price Each
1" x 30 yds	36303	-	-	-	\$21.79
2" x 30 yds	55262	-	36311	-	\$43.58
4" x 30 yds	36289	36315	36316	36317	\$87.13



Self Sticking Vinyl Arrows

- Mounted on easy-to-use dispenser cards
- Durable B-946 material withstands the elements indoors or out

Size	Blk/Ylw	Wht/Grn	Blu/Wht	Qty/Card	Price
2 3/4" x 7"	76507	76503	-	2	\$2.33
1 1/8" x 7"	93242	93257	93247	4	\$2.33
4" x 12"	93390	93396	-	2	\$4.74



ISO 14726 Pipe Banding Tape

- Help reduce accidents and damage to machinery
- Provides 360° visibility
- ISO14726 Marine Standard defines the principle colors for identifying pipes - each color indicates a certain gauge of substances

Roll Size	Yellow	Red	Org	Silver	Price Each
1" x 30 yds	36301	36302	91428	105579	\$21.79
2" x 30 yds	55260	55261	91430	-	\$43.58
4" x 30 yds	36287	-	-	-	\$87.13



Stock Economy Pipe Banding Tape

- B-88 self-wound, non-printable plastic backed cloth tape
- Stock Economy Pipe Banding Tape is ideal for use in indoor color coding applications.

Roll Size	Yellow	Blue	Blk	Price
2" x 60 yds	80184	80187	80191	\$54.55

Custom Pipe Marker Request

www.BradyID.com/pipemarkers

Order Quote Artwork Attached Ship Via: _____ P.O. # or Request # : _____

General Information - Fax completed form to your local distributor

Company Name: _____ Name: _____
 Address1: _____ Phone #: _____
 Address2: _____ Fax #: _____
 City: _____ ST: _____ Zip: _____ Email: _____

Item Information

Self-Sticking B-946		Brady Snap-On B-915		High Performance B-689	
Pipe Outside Diameter	Order By Style	Pipe Outside Diameter	Order By Style	Pipe Outside Diameter	Order By Style
Less than 3/4" OD	3c - (3mrks/card)	3/4" to 1 3/8" OD	A	1/2" to 1 3/8" OD	0
3/4" to 2 3/8"	4 - (4mrks/card)	1 1/2" to 2 3/8" OD	B	1 1/2" to 2 3/8" OD	I
2 1/2 to 7 7/8" OD	1	2 1/2" to 3 7/8" OD	C	2 1/2" to 7 7/8" OD	II
8" and above OD	1HV	4" to 6" OD	D	8" to 10" OD	III
Arrows sold separately.		6 to 7 7/8" OD	F	10+" to 16" OD	IV
		8" to 9 7/8" OD	G	16+" to 22" OD	V
		10" to 15" OD	H	22+" to 26" OD	VI
		Cable Style		High Performance B-681 B-883 (HPHV)	
		3/4" - 5/8" OD	Cable	8" & above OD	HPHV

Markers printed with arrows

Request Data

Legend	Color		Marker	Material	Quantity
	Text	Bkgd			
Line 1	Text	Bkgd	Style		
1.					
2.					
3.					
4.					
5.					
6.					
7.					
8.					
9.					
10.					

Brady standard pipe markers colors are: Yellow, Green, Red, Blue, White, Grey, Brown, Orange, Black, Purple and Clear. Custom colors are available.

Distributor Information

Distributor: _____ Contact: _____
 Account #: _____ Fax #: _____ Phone #: _____

Vinyl Cloth Wire Marker Cards



- Brady's exclusive Zip-Strip® release card lets you easily remove just the markers you need
- Large selection of wire marker cards allow you to choose the wire marking product that precisely meets your application requirements
- Wire markers are .25 inches wide and 1.5 inches long

25 Cards Per Package

Legend	Markers/Card	Catalog #	Price Each
0	36	WM-0-PK	\$43.20
1	36	WM-1-PK	\$43.20
2	36	WM-2-PK	\$43.20
3	36	WM-3-PK	\$43.20
4	36	WM-4-PK	\$43.20
5	36	WM-5-PK	\$43.20
6	36	WM-6-PK	\$43.20
7	36	WM-7-PK	\$43.20

25 Cards Per Package

Legend	Markers/Card	Catalog #	Price Each
8	36	WM-8-PK	\$43.20
9	36	WM-9-PK	\$43.20
1 - 33	33	WM-1-33-PK	\$43.20
34 - 66	33	WM-34-66-PK	\$43.20
67 - 99	33	WM-67-99-PK	\$43.20
100 - 124	25	WM-100-124-PK	\$43.20
125 - 149	25	WM-125-149-PK	\$43.20
A - Z	26	WM-A-Z-PK	\$43.20


Porta-Pack® Wire Marker Books



- Ten pages per book
- Slim, lightweight, pocket-sized book is easy to carry and easy to use
- Numbers...letters...special symbols...NEMA colors
- Includes terminal markers with each wire
- Material - B-500 Vinyl Cloth

Legend	Markers /Legend	Catalog#	Price Each
0 thru 9	45	PWM-PK-1	\$24.61
A-Z and 0-15, (+), (-), (/)	10	PWM-PK-2	\$24.61
1 thru 45	10	PWM-PK-3	\$24.61
1 thru 15	6		
16 thru 90	4	PWM-PK-8	\$24.61
A-Z, (+), (-), (/), (O)	2		

Load Center & Residential Wire Markers



- Fits right on switch or circuit breaker
- Comes in ten page-sized book for convenient use (five cards each of two legends)
- Material - B-500 Vinyl Cloth

Part Number	Size - Inch (mm)	Markers Each Legend	Price Each
PWM-LC-3	1.55 x .20 (39.37 x 5.08)	5	\$24.61

Write-On Self-Laminating Wire & Cable Markers



- Use Brady's labeling pens or other markers to write on legend
- Transparent part over-wraps provide snug fitting, self-laminating shield that resists oil, water and solvents
- For applications above or below ground
- Material - B-292 Vinyl

Legend	Marker Size Inch (mm)	Markers Per Book	Size of Write-on Area Inch (mm)	Part Number
Blank/Write-on	.75 x 1.75 (19.00 x 44.40)	120	.75 x .50 (19.00 x 12.70)	PWC-PK-1
Blank/Write-on	1.00 x 3.00 (25.40 x 76.20)	60	1.00 x .75 (25.40 x 19.00)	PWC-PK-3
Blank/Write-on	1.00 x 6.00 (25.40 x 152.40)	30	1.00 x 1.00 (25.40 x 25.40)	PWC-PK-6
Blank/Write-on	1.00 x 3.00 (25.40 x 76.20)	30	1.00 x .75 (25.40 x 19.00)	PWC-PK-36
	1.00 x 6.00 (25.40 x 152.40)	15	1.00 x 1.00 (25.40 x 25.40)	

Price Each \$30.86

Lean/Visual Workplace

www.BradyID.com/visualworkplace

Create Workplace Visuals with MarkWare™ Lean Tools Software

Lean/Visual Workplace



Ideas, Best Practices & Solutions

MarkWare Lean Tools software lets you easily create signs, labels, tags and other visuals right on your computer. Post critical information at the point of need to ensure that best practices remain readily visible, clearly understood, and consistently adhered to. Perfect for use in 5S, Standard Work, Total Productive Maintenance and other lean initiatives.

Additional Features:

- Includes over 1,000 safety and industrial pictograms
- Select from 15 different bar code symbologies
- Import logos, photos, and other graphics
- Merge data from spreadsheets and databases

Catalog No.	Description	Price Each
20700L	MarkWare™ LEAN Software	\$624.37
20711L	MarkWare™ LEAN Software & Laminating Kit	\$724.89

NEW!

BBP®31 Sign & Label Printer

Quickly and easily create lean visuals with the new BBP®31 Sign & Label Printer and MarkWare™ Lean Software.

View page 132 for more informations or visit www.BradyID.com/bbp31



MarkWare™ Lean Tools Software



Tool Storage



Part Management



Process Identification



Work Instructions

Visual Equipment Controls

MarkWare Lean Tools software also includes templates that allow you to quickly create multicolor gauge labels, lube instructions, oil level indicators and more.*



Gauge Labels




PM Instructions



Oil Level Indicators



Alignment Guides



Drive Tension Indicator

* Multi-color labels and cut out labels available only on GlobalMark® Color & Cut and Multicolor models. Single-color labels available on GlobalMark monochrome and BBP®31 model printers

Tool Board & Workbench Marking Supplies

- These vinyl sheets and tapes are designed for use on tool boards, work benches, storage shelves, desktops and other non-floor applications.
- Made of 0.125 mm vinyl with industrial-grade adhesive.
- Sticks securely to a wide range of surfaces and resists scratching.
- Won't peel, crack or fade when exposed to common cleansers, solvents or sunlight



Shadow Vinyl Rolls

- Quickly and easily create tool shadows to exact size and shape.
- Simply place tool or other object on vinyl, trace outline with pen and cut out with scissors.
- Roll: 12" w x 12' long

Catalog Number	Color	Price
113245	Red	\$40.79
113248	Green	\$40.79
113249	Black	\$40.79
113247	Yellow	\$40.79
113246	Blue	\$40.79



Corner Marking Tape

- Use corner marks to quickly define storage locations on workbenches, desktops & shelves.
- L-shaped marks: 1" w x 1" T (750pcs.)
- T-shaped marks: 1.5" w x 1" T (545pcs.)
- Roll Length is 50'

Color	L-shaped	T-Shaped
	\$27.56	\$27.56
Red	113260	113265
Green	113263	113268
Black	113264	113269
Yellow	113262	113267
Blue	113261	113266



Border Marking Tape

- Solid borders, dividing lines.
- Place color-coded bands on tools for easy identification when similar equipment is used by different individuals or departments.
- Roll Length is 50'

Color	1/2" wide	1/4" wide
	\$22.05	\$16.54
Red	113255	113250
Green	113258	113253
Black	113259	113254
Yellow	113257	113252
Blue	113256	113251

NEW! Premium 5S Marking Kits

Brady's Premium 5S Marking Kits provide everything you need to 5S your facility, enhancing workplace organization and efficiency.



* Not all kit contents shown

Catalog No.	Description	Price
142109	Premium Kit	\$449.95
142110	Premium Kit with IDXPERT™ Printer	\$999.95
142111	Premium Kit with BMP®71 Label Printer	\$1,599.95

Premium Kit includes:

- **ToughStripe® floor marking tapes** (1 roll of yellow, red, blue, green)
 - 4 Rolls of 2" floor tape (yellow, red, blue, green)
 - 4 Packages of 2" L-shaped corner marks (yellow, red, blue, green)
- **Toolboard / workbench marking tapes** (1 roll of black, red, blue, green)
 - 4 Rolls of 12" shadow vinyl (black, red, blue, green)
 - 4 Rolls of 1/2" border tape (black, red, blue, green)
 - 4 Rolls of 1/2" L-shaped corner marks (black, red, blue, green)

Premium Kit with IDXPERT™ Printer includes:

All Contents of Premium 5S Marking Kit, plus:

- IDXPERT™ Continuous Only Label Printer
- AC adaptor
- 3 Black on white tape cartridges (1/2", 1", 1 1/2")
- 1 Black on yellow tape cartridge (1 1/2")
- 1 Red on white tape cartridge (1 1/2")

Premium Kit with BMP®71 Label Printer includes:

All Contents of Premium 5S Marking Kit, plus:

- BMP®71 Printer with hard carrying case
- Charger/AC power adaptor
- 3 White vinyl tape cartridges (1/2", 1", 2")
- 1 Yellow vinyl tape cartridge (2")
- 2 Ribbon cartridges (black, red)




Lean/Visual Workplace

www.BradyID.com/visualworkplace

Lean information boards expand shop floor communication

Use lean communication boards to:

- Track key performance indicators
- Post schedules and assignments
- Submit ideas and work requests
- Provide lean activity updates
- Report audit / inspection results
- Recognize achievements



Durable, yet light weight

- Made of 1/4"-thick extra heavy duty preboard with polystyrene foam core
- Withstands industrial environments without warping, cracking or fading
- For indoor use only

Customize displays to your needs

- Two colors and two sizes available – 4 or 6 panel format
- Add headings and subheadings using a permanent marker or Brady industrial label printer
 - Print on Brady clear vinyl for a clean, professional look. Using Brady repositionable vinyl also makes it easy to change headings and re-purpose boards for other uses. For more info on Brady printers, see page 6 of the Visual Workplace catalog or visit www.BradyID.com/visualworkplace.
- Adhere either document holders or dry erase panels
 - Document holders allow you to easily display charts, graphs and spreadsheets created on your computer
 - Use dry erase panels for displaying metrics and schedules that are frequently updated, and for recording shopfloor improvement ideas and maintenance requests



Attaches to board using velcro strip

Shown with optional floor stand



Lean Communication Boards

Catalog #	Description	Dimensions	Price
114612	Gray 4-Panel Board w/ 4 document holders & wall mounting hardware	25"w X 34"h	\$136.50
114611	Blue 4-Panel Board w/ 4 document holders & wall mounting hardware	25"w X 34"h	\$136.50
114614	Gray 6-Panel Board w/ 6 document holders & wall mounting hardware	37"w x 34"h	\$178.50
114613	Blue 6-Panel Board w/ 6 document holders & wall mounting hardware	37"w X 34"h	\$178.50

Display Board Accessories

Catalog #	Description	Price
112633	Document holders 10/pack	\$61.95
114610	Dry erase panels 5/pack	\$20.95
112632	Dry erase markers (3 markers, 1 eraser)	\$19.95
112631	Floor Stand (works with 4 and 6 panel displays)*	\$204.75

*Holds one or two boards back to back. Made of powder-coated steel.

! Custom Lean Boards

Brady can also custom print headings, company logos, etc., to customer specifications. Turnaround is fast - ships within 3-5 days. Call Brady Customer Service at 888-292-3946 for ordering details.



Visual Workplace e-Learning Training Courses

Train your employees on Visual Workplace with Brady's new online training courses. The courses feature interactive features, real-life application scenarios and quizzes to facilitate learning and remembering. Employees can access the courses online from your facility, which eliminates the costs of off-site training. Certificate available upon completion.

Only available at www.BradyID.com/elearning

Catalog No.	Description	Price
142256	Introduction to Visual Workplace (approx. 30-40mins)	\$29.95
142257	Visual 5S: Optimizing Workplace Organization (approx. 30-40mins)	\$29.95
142258	Visual TPM: Enhancing Equip. Reliability & Maint. Efficiency (approx. 30-40mins)	\$29.95
142259	e-Learning Bundle: (1) Intro to VW, (1) Visual 5S and (1) Visual TPM	\$74.95

Visual Workplace Training Materials

Visual Workplace Foundations Training Kit

- Provides a comprehensive foundation in core visual workplace concepts, principles, and tools of proven value for both lean novices and experts.
- Produced by Dr. Gwendolyn D. Galsworth, PhD, founder of the QMI/Visual-Lean® Institute and recognized expert on optimizing workplace productivity through the technologies of the visual workplace.
- Covers visual techniques and best practices that are critical to the success and sustainment of any lean, 5S or kaizen initiative.
- See 150 visual workplace examples, and listen as actual users of the system share their insights and experiences.
- Also includes an audio CD set with additional coaching for managers and trainers on effectively training and leading a visual workplace conversion; plus a 230-page Visual Workplace Handbook with over 200 photos.
- First DVD, Basics of Visual Thinking, also sold separately for those wishing to get an overview of the series content and instructional approach.



Contents:

- 6 DVD Set (4 modules + overview)
- 2-CD Audio Set
- 1 Associate Handbook (230 pages, 200+ photos)
- 1 Tote Bag

Catalog #	Description	Price Each
113238	Complete Training Kit	\$1,044.75
113240	2-CD Audio Set	\$31.45
113239	1 Associate Handbook	\$52.45
113244	1st DVD: Basics of Visual Thinking	\$314.95



Visual Workplace, Visual Thinking Book

- Written by Dr. Gwendolyn Galsworth, PhD, this book positions workplace visibility as a powerful partner on your company's lean journey.
- Provides concepts, principles, frameworks, and models for creating a fully-functioning visual enterprise through visual workplace technologies: Visual Order, Visual Standards, Visual Displays, Visual Metrics, Visual Problem Solving, Visual Controls, Visual Pull Systems, and Visual Guarantees (poka yoke devices).
- 200+ pages, with 200 full-color photographs and 50 charts.

Catalog #	Description	Price Each
113241	Visual Workplace, Visual Thinking Book	\$68.20


Work That Makes Sense Book

At last, a book that explains workplace visibility as a comprehensive strategy for eliminating abnormalities, sustaining lean gains, and aligning and unifying the work culture. Written by Dr. Gwendolyn Galsworth, PhD, *Work That Makes Sense* is a complement to her *Visual Workplace, Visual Thinking* book which shows you how to implement, coach, support, and sustain visual inventiveness on the operator-level.

Catalog #	Description	Price
142132	Work That Makes Sense Book	\$59.95

Lean Machines for World-Class Manufacturing & Maintenance

- Written by Robert M. Williamson, an educator, consultant, and writer on the subjects of Total Productive Maintenance (TPM) and Lean Equipment Management.
- This book explains how visual systems can be applied to simplify the interactions between people and machines, eliminating many of the equipment-related wastes in the workplace.
- Learn how visual controls improve equipment performance, simplify routine maintenance, plus reduce equipment training time by 60 to 80 percent. You will also see how visuals can facilitate the early detection of operating abnormalities and raise the success rate of operator-based care programs.



Visual Systems Presentation CD-Rom

- Companion to Lean Machines book.
- Powerpoint slides provide access to the many different full-color examples of visual systems referenced in the book.
- Handout materials and facilitator's notes can also be printed from the CD-ROM for use in the classroom.

Catalog #	Description	Price Each
113242	Lean Machines Book	\$36.70
113243	Visual Systems Presentation CD	\$36.70

ToughStripe® Floor Marking

www.BradyID.com/toughstripe



TOUGHSTRIPES® Floor Marking

ToughStripe® floor marking products are made with Brady's new B-514 polyester. ToughStripe products are ideal for marking aisles, passageways and storage locations, and pointing out important safety equipment and egress paths.

- Exceeds safety standards for clean, dry non-slip surfaces per ANSI A1264.2-2006 and OSHA 1910.22
- 2 mil thickness
- Service temperature range of 0F – 129F
- Resists harsh chemicals
- For maximum performance, apply ToughStripe floor tape to flat, non-coated, concrete.



Superior Durability

Spend less time replacing damaged or worn lines for a better-looking, more efficient facility.

- Withstands forklift traffic without tearing or lifting
- Low-profile design minimizes tears and scratches from skids, pallet jacks, etc.
- Rugged polyester with ultra-aggressive adhesive



Easy Application

Quickly lay down smooth, straight lines – without the help of coworkers.


- Can be easily applied by one person working alone
- Stiff polyester with liner prevents tape stretching and reduces wrinkles and wavy, uneven lines
- No special floor preparation required – just clean with common cleansers



High Visibility

Get the same visibility of painted floor markings – and pay less.

- High-gloss surface shines like new paint
- Low profile minimizes debris buildup along the edges that occurs with thicker (extruded) floor tapes
- Surface resists marks and smudges and cleans up like new
- Available in a variety of high-impact colors



Diecut Shapes

Utilize different shapes, colors and sizes for more effective, durable floor markings.

- Dashes, dots, arrows, footprints, and corner marks (L, T and + shapes)
- Longer lasting markings – Minimizes the risk of damage and facilitates fast repair
- Select dashes, dots and arrows are pre-spaced on transfer tape, making it incredibly easy to lay down straight, evenly spaced lines.

Painless Removal

Easily remove floor markings without damaging the floor or leaving adhesive residue.

- Does not chip and flake when being removed – comes off in one piece
- Clean removal without any unsightly adhesive residue or damage to the floor

Print-On-Demand Capabilities

Create custom-printed floor labels using your Brady label printer!

- Same durability and performance as ToughStripe™ floor marking tape
- Easy 3-step process: print label, position on floor, apply overlamine
- Supplied as cartridge for use with GlobalMark®2 Label Maker and BMP®71 Label Printer. See page 90 for available parts.



ToughStripe® Floor Marking

www.BradyID.com/toughstripe

ToughStripe® Floor Marking Polyester Tape

ToughStripe® floor marking products are made with Brady's new B-514 polyester. ToughStripe products are ideal for marking aisles, passageways and storage locations, and pointing out important safety equipment and egress paths.

- Exceeds safety standards for clean, dry non-slip surfaces per ANSI A1264.2-2006 and OSHA 1910.22
- 2 mil thickness
- Service temperature range of 0F – 129F
- Resists harsh chemicals



Floor Marking Tape B-514

	Black	White	Red	Green	Blue	Orange	Yellow	Black/Yellow /////	Red/White /////	Black/White /////	Price
2" x 100'	104310	104311	104313	104315	104314	104316	104312	104317	104318	104319	\$40.00
3" x 100'	104340	104341	104343	104345	104344	104346	104342	104347	104348	104349	\$58.00
4" x 100'	104370	104371	104373	104375	104374	104376	104372	104377	104378	104379	\$76.00



Pre-Spaced Shapes (Spaced 18" Apart) B-514

	Black	White	Red	Green	Blue	Yellow	Price
3.5" x 100' - 55 dots	104525	104522	104521	104520	104524	104523	\$70.00
2" x 5" x 100' - 52 arrows	104554	104555	104526	104527	104528	104529	\$112.00
2" x 8" x 100' - 46 dashes	142178	142177	142179	142181	142180	104556	\$63.00



Dots - 350 / Roll B-514

	Black	White	Red	Green	Blue	Yellow	Price
3.5" Dia	104404	104405	104400	104401	104402	104403	\$122.39



Corner Marks - "L" 20 / Package B-514

	Black	White	Red	Green	Blue	Yellow	Price
2" x 5"	104434	104435	104430	104431	104432	104433	\$25.00
3" x 8"	104446	104447	104442	104443	104444	104445	\$36.25
4" x 10"	104458	104459	104454	104455	104456	104457	\$52.56



Arrows 100 / Package B-514

	Black	White	Red	Green	Blue	Yellow	Price
2" x 5"	104416	104417	104412	104413	104414	104415	\$115.00
3" x 8"	104422	104423	104418	104419	104420	104421	\$174.24
4" x 10"	104428	104429	104424	104425	104426	104427	\$221.00



Center Marks - "+" 20 / Package B-514

	Black	White	Red	Green	Blue	Yellow	Price
2" x 5"	104470	104471	104466	104467	104468	104469	\$25.00
3" x 8"	104476	104477	104472	104473	104474	104475	\$36.25
4" x 10"	104482	104483	104478	104479	104480	104481	\$52.56



Foot Prints - 10 / Package (5 Right - 5 Left) B-514

	Black	White	Red	Green	Blue	Yellow	Price
10' x 3.5"	104410	104411	104406	104407	104408	104409	\$32.00



Divider Marks - "T" 20 / Package B-514

	Black	White	Red	Green	Blue	Yellow	Price
2" x 5"	104440	104441	104436	104437	104438	104439	\$25.00
3" x 8"	104452	104453	104448	104449	104450	104451	\$36.25
4" x 10"	104464	104465	104460	104461	104462	104463	\$52.56

ToughStripe® Floor Marking

www.BradyID.com/toughstripe

Lean/Visual Workplace

GlobalMark™ Toughstripe Labels with Overlamine

- Create custom-printed floor labels using your GlobalMark™2 Label Maker!
- Revolutionary new B-514 material has ultra aggressive adhesive
- Withstands forklift and pallet jack traffic without tearing or lifting
- Easy 3-step process: print label, position on floor, apply overlamine
- Each roll ships with a roll of clear overlamine



NOTE: Specialty black ribbon catalog #96089 required to print on ToughStripe floor tape. Use standard white ribbon catalog #76741 for white text.

Color		1.125" x 100'	Catalog Number		
			2.25" x 100'	3" x 100'	4" x 100'
			Price \$284.07	Price \$311.99	Price \$347.73
White		142155	142154	142156	142157
Black		142159	142158	-	142160
Yellow		142162	142161	142163	142164
Red		142166	142165	-	142167
Blue		142169	142168	-	142170
Green		142172	142171	-	142173
Orange		142175	142174	-	142176



BMP®71 Toughstripe Labels with Overlamine

- Create custom-printed floor labels using your BMP71 Label Printer!
- Same durability and performance as ToughStripe floor marking tape
- Easy 3-step process: print label, position on floor, apply overlamine

NOTE: Specialty black ribbon catalog #M71-R6000 required to print on ToughStripe floor tape. Use standard white ribbon catalog #M71-R4400-WT for white text.

Description		Catalog Number	
		1" x 50' \$122.40	2" x 50' \$183.70
White		M71-1000-483-WT-KT	M71-2000-483-WT-KT
Black		M71-1000-483-BK-KT	M71-2000-483-BK-KT
Yellow		M71-1000-483-YL-KT	M71-2000-483-YL-KT
Red		M71-1000-483-RD-KT	M71-2000-483-RD-KT
Blue		M71-1000-483-BL-KT	M71-2000-483-BL-KT
Green		M71-1000-483-GN-KT	M71-2000-483-GN-KT
Orange		M71-1000-483-OR-KT	M71-2000-483-OR-KT



ToughStripe® Floor Marking

www.BradyID.com/toughstripe

Premium Kit includes:

ToughStripe® floor marking tapes (1 roll of yellow, red, blue, green)

- 4 Rolls of 2" floor tape (yellow, red, blue, green)
- 4 Packages of 2" L-shaped corner marks (yellow, red, blue, green)

Toolboard / workbench marking tapes (1 roll of black, red, blue, green)

- 4 Rolls of 12" shadow vinyl (black, red, blue, green)
- 4 Rolls of ½" border tape (black, red, blue, green)
- 4 Rolls of ½" L-shaped corner marks (black, red, blue, green)



* Not all kit contents shown

Premium Kit with IDXPERT™ Printer includes:

All Contents of Premium 5S Marking Kit, plus:

- IDXPERT™ Continuous Only Label Printer
- AC adaptor
- 3 Black on white tape cartridges (½", 1", 1½")
- 1 Black on yellow tape cartridge (1½")
- 1 Red on white tape cartridge (1½")

Premium Kit with BMP®71 Label Printer includes:

All Contents of Premium 5S Marking Kit, plus:

- BMP®71 Printer with hard carrying case
- Charger/AC power adaptor
- 3 White vinyl tape cartridges (½", 1", 2")
- 1 Yellow vinyl tape cartridge (2")
- 2 Ribbon cartridges (black, red)

Premium 5S Marking Kits With ToughStripe® Floor Marking Tape

Brady's Premium 5S Marking Kits provide everything you need to 5S your facility, enhancing workplace organization and efficiency.

Catalog No.	Description	Price
142109	Premium Kit	\$499.95
142110	Premium Kit with IDXPERT™ Printer	\$999.95
142111	Premium Kit with BMP™71 Label Printer	\$1,599.95



Online Video:
www.BradyID.com/toughstripe



How To Apply ToughStripe Floor Marking Tape

1. Clean Surface

Sweep and clean intended application area and allow floor to dry completely before application.

2. Position Tape

Keeping the liner in place, position tape along entire desired path.

3. Remove Liner

Start at one end and peel the liner away from the tape while smoothing down the tape and providing lamination pressure.



*For maximum performance, apply ToughStripe floor tape to flat, non-coated, concrete.

Want More Information On Floor Marking?

Download the free 5S Floor Marking Color Reference Guide to learn how strategic floor marking can stabilize operations and sustain improvements.

- Color guidelines for marking aisles, equipment areas, & safety hazards
- How-to tips for visually delineating work areas and pathways
- Best practices for identifying designated storage locations for materials, products tools and equipment
- Real plant photos and examples

Download available at: www.BradyID.com/visualworkplace



ToughStripe® Floor Marking

www.BradyID.com/visualworkplace

Brady B-534 ToughStripe® Floor Signs with Anti-Skid Treads

Brady B-534 ToughStripe Floor Signs are made with Brady's new B-534 polyester. They are specifically designed to alert workers of potential dangers and enforce protective equipment requirements.

- Exceeds safety standards for clean, dry non-slip surfaces per ANSI A1264.2-2006 and OSHA 1910.22
- Service temperature range of 0°F – 129°F
- 3 mil thickness. 14" x 18" Square or 17" Diameter Circle
- Price \$38.70



104486



104487



104507



104489



104495



104492



104493



104494



104496



104490



104488



104491



104497



104498



104500



104506



104499



104502



104503



104504



104505



104510



104501



104508



104509



104511



104512



104513



Also available: Custom ToughStripe® Tape

- Pre-printed ToughStripe® Tape with your custom message
- Die cut numbers and letters for safety, lean and other applications
- Specific die cut shapes
- Any color you desire, just provide a PMS #
- Striped or checkered tape is available

Contact Brady Customer Service to order your custom ToughStripe® Tapes.



BradyGlo™ Egress Marking

The 2009 versions of the International Building Code (IBC), International Fire Code (IFC) and the National Fire Protection Agency's (NFPA) 101 Life Safety Code contain new provisions for the means of egress in most new and pre-existing buildings with five or more stories.

Luminous (glow-in-the-dark) egress path markings are now required for the full width of every stair and handrail, among other markings. Brady offers a complete line of egress marking products that meet the current requirements for the 2009 means of egress regulations.



BradyGlo™ Floor Tapes

- Made of B-324 phosphorescent surface printed polyester
- Designed for safe Low Level Lighting egress pathway marking during power outages and emergency situations

Solid

Catalog #	Size	Price Each
76432	2" x 15' BradyGlo Tape	\$67.17
76433	3" x 15' BradyGlo Tape	\$88.36



High Intensity Marking Tape

- 1" x 50' tape made of BradyGlo™ High Intensity Self Sticking Polyester
- IBC/IFC compliant or NYC approved styles
- Ideal for marking leading edges of steps and landings, perimeter demarcation lines, door frames, and handrails.

IBC/IFC Compliant

Cat. No.	Description	Price Each
114634	IBC/IFC Compliant Marking Tape	\$181.50
114636	IBC/IFC Compliant Anti-Slip Marking Tape	\$194.50

NYC Approved

Cat. No.	Description	Price Each
81873	NYC Approved Marking Tape	\$60.59
81729	NYC Approved Anti-Slip Marking Tape	\$68.71



High Intensity Obstacle Tape

- 1" x 50' tape made of BradyGlo™ High Intensity Self Sticking Polyester
- IBC/IFC compliant or NYC approved styles
- Clearly marks obstacles that protrude into the egress path, such as standpipes, hose cabinets, wall projections, and restricted height areas.

IBC/IFC Compliant

Cat. No.	Description	Price Each
114635	IBC/IFC Compliant Obstacle Tape	\$183.50

NYC Approved

Cat. No.	Description	Price Each
81869	NYC Approved Obstacle Tape	\$64.82



BradyGlo™ Arrow Tape

- BradyGlo™ B-324 tapes exceed ASTM E 2072-00 standard specifications
- Designed for safe LLL (Low Level Lighting) egress pathway marking during power outages and emergency situations
- Standard package: one 5 yd. roll

V-Style

Catalog #	Width	Price
90971	2" Arrow Tape	\$76.19
90972	3" Arrow Tape	\$93.78

Arrow-Style

Catalog #	Width	Price
90973	2" Arrow Tape	\$76.19
90974	3" Arrow Tape	\$93.78

Stripes


Catalog #	Width	Price
76430	2" Arrow Tape	\$76.19



BradyGlo™ Handrail Covers

- BradyGlo™ Handrail Covers can be easily installed onto existing handrails, and adhesive can be added to make the installation permanent.
- Available for both round and square handrails.
- Snap-fit over existing handrails
- Made from durable extruded polycarbonate
- Co-extruded photoluminescent glow channel

Description	1/each	8/pack
	\$27.95	\$199.95
Square - Black	114904	114905
Square - Gray	114906	114907
Round - Black	114908	114909
Round - Gray	114910	114911



BradyGlo™ Stair-Nosing

- Made from durable, 40% glass-filled polyurethane material
- Cost-effective alternative to aluminum stair-nosing
- Molded glow channel with both chemical and mechanical interference fit
- Size: 1.32" H x 48" W x 3" D

Description	1/each	10/pack
	\$49.95	\$469.95
High Traffic - Blk	114898	114899
High Traffic - Gray	114900	114901
	\$39.95	\$379.95
Low Traffic - Blk	114902	114903

Floor Marking Tape

www.BradyID.com/visualworkplace

Mark Aisles & Passageways

CFR 1910.22(b)(2)

Permanent aisles and passageways must be appropriately marked.

1910.22(b)(1)

Where mechanical handling equipment is used, sufficient safe clearances shall be allowed for aisles, at loading docks, through doorways and wherever turns or passage must be made. Aisles and passageways shall be kept clear and in good repairs, with no obstruction across or in aisles that could create a hazard.



Yellow and Black Caution Tape-29 CFR

1910.145(c)(2)

Caution signage shall be used to warn against potential hazards or to caution against unsafe practices.



Aisle Marking Tapes

- Made of long-wearing B-725 vinyl tape
- Applies quickly and sticks tightly
- Standard package: one 36 yd. Roll
- Tape does not work with Universal Line Applicator

Size	Catalog Number					Price
	Yellow	Red	Green	White	Blue	
2"	58200	58201	58202	58203	58220	\$36.42
3"	58250	58251	58252	58253	58221	\$55.19
4"	102838	102836	102834	102837	102833	\$69.26



Stripes & Solid Reflective Tape

- Give an extra margin of safety in low light conditions.
- Made of B-957 reflective tape
- Each roll: 15 ft.

Solid Color Tapes

Width	Catalog Number			Price
	White	Yellow	Orange	
2"	78985	78986	78989	\$57.91
3"	-	78988	-	\$75.92

Stripes

Width	Catalog Number		Price
	Black/Yellow	Red/White	
2"	76308	76309	\$65.48
3"	76312	76313	\$83.73



Striped Warning & Check Tape

- Made of B-950 vinyl with permanent adhesive
- Locked-in colors - sealed beneath protective layer of abrasion resistant clear vinyl
- Stands up to the toughest indoor conditions
- Meets OSHA specifications
- Standard package: one 18 yd. roll

Stripes

Wid.	Catalog Number					Price
	Blk/Ylw	Rd/Wht	Blk/Wht	Grn/Wht	Mag/Ylw	
1"	55300	-	-	-	-	\$20.18
1½"	55301	-	-	-	55312	\$30.18
2"	55302	55296	55292	90019	55313	\$38.86
3"	55303	55297	55293	-	55314	\$55.27

Checks

Width	Catalog Number		Price
	Black/Yellow	Black/White	
2"	76317	76316	\$39.86

Floor Marking Tape

www.BradyID.com/visualworkplace



Warning Message Tapes

- Stands up to the toughest indoor conditions
- Meets OSHA specifications
- Each roll: 60 ft.

Cat. No.	Legend	Color	Price
58255	Caution w/ Stripes	Black/Yellow	\$69.00
58257	Stripes Only	Black/Yellow	\$69.00



Hazard Marking Diecut Cleats

- Made of B-916 grit coated polyester tape
- Standard package: 24 cleats

Catalog Number	Legend	Size	Price
78160	Caution	6" x 24"	\$292.43
78163	Watch Your Step	6" x 24"	\$292.43
78161	Reflective Stripe	6" x 24"	\$256.04
78162	Photo-Lum Stripe	6" x 24"	\$256.04
78192	Black(50/pkg)	3/4" x 24"	\$55.31
78195	Black (50/pkg)	6" x 24"	\$326.18



Footprints

- Footprint size: 12"
- Bright yellow color or B-324 Glow-in-the-dark with 10+ glow life

Catalog Number	Material	Qty.	Price
55356 (Left)	Yellow Vinyl	1	\$2.35
55357 (Right)	Yellow Vinyl	1	\$2.35
31550	Removable	5 sets	\$76.97



Warning Stripe Anti-Skid Tape

- Provides visibility of hazardous areas
- B-916 Adhesive backed plastic tape with an oxide grit coating

Catalog Number	Color	Size	Price
78146	Black & Yellow	1" x 60'	\$44.90
78147	Black & Yellow	2" x 60'	\$88.03
78148	Black & Yellow	3" x 60'	\$134.71
78149	Black & Yellow	4" x 60'	\$179.56
78150	Black & Yellow	6" x 60'	\$230.66



Anti-Skid Floor Tape

- Made of B-916 adhesive-backed polyester tape coated with durable aluminum oxide grit
- Bonds permanently to clean, dry floors
- Works indoors and outdoors
- Withstands grease and oil

Catalog Number	Color	Size	Price
78189	Black	1" x 60'	\$34.88
78190	Black	2" x 60'	\$69.91
78198	Red	2" x 60'	\$76.37
78091	Safety Yellow	2" x 60'	\$76.37
78188	Clear	2" x 60'	\$76.37
78191	Black	4" x 60'	\$138.31
78092	Safety Yellow	4" x 60'	\$152.96
78193	Black	6" x 60'	\$209.55
78194	Black	12" x 60'	\$414.16



Heavy Duty Anti-Skid Tapes

- Aggressive adhesive system engineered to withstand harsh applications
- Durable "high slip resistance" with deeply textured silicon carbide grit
- Ideal for machinery, forklifts, loading docks, ramps and platforms
- **NFSI** - National Flooring Safety Institute certified for "high traction"
- Each roll: 60 ft

Catalog Number	Color	Size	Price
110020	Black	2" x 60'	\$74.11
110019	Black	4" x 60'	\$146.60
110018	Black	6" x 60'	\$222.13
110017	Black	12" x 60'	\$439.02

Lean/Visual Workplace

www.BradyID.com/visualworkplace



Roll Mounted Dots

- Made of B-933 vinyl tape
- Single roll of dots will mark over 1,000 lineal feet of aisle or passageway
- Standard package: one roll of 1,000 dots

Catalog #	Description	Price
55332	3" Yellow Dots	\$296.69
55350	3" White Dots	\$296.69



Vinyl Dots

- Made of B-933 self-sticking vinyl tape
- Standard package: 500 dots

Catalog #	Description	Price
55324	2" Yellow	\$85.69
55325	3" Yellow	\$148.43
55338	3" Red	\$148.43
55326	4" Yellow	\$256.82
55327	5" Yellow	\$344.48



Vinyl Arrows

- Made of B-933 vinyl tape
- Standard package: 100 arrows per pkg.

Catalog #	Description	Price
55352	2" Yellow Vinyl Direction Arrows	\$20.37
55353	3" Yellow Vinyl Direction Arrows	\$35.91
55354	4" Yellow Vinyl Direction Arrows	\$60.97
55355	5" Yellow Vinyl Direction Arrows	\$83.69

Bradystake™ Warning Stakes




Blank and Reflective Bradystake™ Warning Stakes

- Blank stakes with no sign assembly
- Stake size: 66" tall, 3 3/4" wide

Catalog No.	Color	Price
96950	Orange With Points	\$26.07
96951	Yellow With Points	\$26.07
96921	Yellow Without Points	\$26.07
96952	Blue With Points	\$26.07
96953	Green With Points	\$26.07
96954	White With Points	\$26.07
96928	White Without Points	\$26.07
96955	Red With Points	\$26.07
96929	Red Without Points	\$26.07
96957	Dark Brown With Points	\$26.07
96922	Orange on White Reflective	\$57.02
96923	Black on Yellow Reflective	\$57.02

Bradystake™ Anchors

- Made of resilient, long-lasting spring steel
- For added stability in loose and sandy soil
- Catch soil around the stake preventing unauthorized removal
- As a custom order, anchors can be attached to Bradystake™ Warning Stakes at the factory for quick field installation
- Available in a kit for customer installation. Kit includes: anchors for five stakes, fasteners and instructions



1. Profile of stake with anchor
2. Anchor compresses against stake during installation
3. Anchor catches surrounding soil and prevents removal

Catalog No.	Description	Price
97084	Bradystake™ Anchors	\$27.71

Bradystake™ Warning Stake Labels

- Made of B-302 polyester
- Decal size: 14" x 3" (H x W)
- 1" blank area at bottom will accommodate separate label with company name and telephone number
- Avoid custom lead times by ordering these stock labels with Blank Bradystake™ Warning Stakes (sold separately above)

Catalog No.	Description	Price
85406	Bradystake™ Labels	\$6.73



SAFETY COLOR CODE FOR MARKING PHYSICAL HAZARDS

1910.144(a)

Use yellow and black for physical hazards, red and white for fire protection equipment, black and white for traffic and housekeeping markings, magenta and yellow for radiation hazards.



Pennant Barricade Tape

- Tough and durable flag barricade can be used repeatedly
- Pennants are 18" x 18" triangles spaced evenly across tape

Catalog No.	Size	Price
58388	83 ft (15 Pennants)	\$79.13
58389	113 ft (25 Pennants)	\$114.93



Re-Pulpable Barricade Tape

- Made of 100% strong woven, biodegradable cotton material
- Tape will break down if accidentally introduced into the system
- Standard package: one roll

Catalog Number	Legend	Color	Size	Price
91083	Caution	Black/Yellow	3" x 50 yds.	\$40.45
91084	Danger	Black/Red	3" x 50 yds.	\$40.45



Barricade Tape

- Provides fast, on-the-spot warning
- Made of non-adhesive B-912 Polyethylene
- Standard package: one roll

Legend	Color	Catalog No.	3" x 200'	3" x 1000'
CAUTION	Blk/Ylw	91212		91450
CAUTION DO NOT ENTER	Blk/Ylw	91224		91451
DANGER	Blk/Ylw			91455
CAUTION DO NOT ENTER	Blk/Ylw	91256	91257	
DANGER	Blk/Red	91200		91201
DO NOT ENTER	Blk/Red			102824
Price Each			\$33.36	\$63.13



Woven Barricade Tape

- Made of B-903 polypropylene
- Contains ultraviolet inhibitors for permanent outdoor marking
- Standard package: one roll

Catalog Number	Size	Color	Price
91172	3/4" x 150'	Black/Yellow	\$8.85
91173	3/4" x 150'	Magenta/Yellow	\$8.85
91175	3/4" x 150'	Black/Red	\$8.85
91176	2" x 200'	Black/Yellow	\$25.78
91179	2" x 200'	Black/Red	\$25.78



Reinforced Barricade Tape

- Provides fast, on-the-spot warning
- Standard package: one roll
- 250 lbs tensile strength

Legend	Color	Size	Catalog Number
CAUTION	Blk/Ylw	3" x 500'	91100
CAUTION DO NOT ENTER	Blk/Ylw	3" x 500'	91102
	Blk/Ylw	3" x 500'	91104
Price Each			\$77.93



Tensabarrier™ Barricade System

- Black posts are 40" high
- Pull out black/yellow belt is 7.5' long
- 14" diameter base weighs 26 pounds

Catalog Number	Description	Price
80125	Post w/ Black/White Stripe Belt	\$366.50
80127	Post & "CAUTION-DO NOT ENTER"-Belt	\$366.50

Lean/Visual Workplace

www.BradyID.com/visualworkplace



BradyLink Warning Posts

- Bases and tops are made of polyethylene - posts are made of polystyrene
- Non-conductive, Non-rusting, Fillable base
- Post dimension: Lg - 3" O.D., Sm - 2.5" O.D.
- Post height: Lg - 41", Sm - 40"
- Base dimension: Lg - 16" dia., Sm - 14" dia

Large Posts

Size	Black	White	Yellow	Price
1/box	92116	92117	92118	\$74.16
6/Box	92119	92120	92121	\$422.77

Small Posts

Size	Black	Yellow	Price
6/Box	80943	80944	\$378.03



Striped Warning Posts

- Barricade potentially hazardous areas with portable, non-rusting, polyethylene posts & chain
- Black & Yellow striped posts come with tops and fillable bases
- Not intended to support heavy weight

Non-Reflective

Size	Large Blk/Yellow	Large Blk/Mag	Sm Blk/Ylw	Price
1/box	92122	92126	-	\$105.46
6/Box	92123	92127	80946 (\$557.40)	\$611.01

Reflective

Size	Large Blk/Yellow	Price
6/Box	92125	\$643.98



BradyLink Warning Chain and Links

- Made of polyethylene
- Link design prevents kinking
- Standard package: 100 feet for chain,
- 36 Links per package for chain
- Indoor Use Only

100' Chain

Size	Yellow	White	Orange Blk/Ylw	Price	
1½"	78234	78235	-	\$186.30	
2"	78238	78239	78241	78254(\$250.66)	\$217.69
3"	37860	-	-	\$414.52	

Box of 36 Links

Size	Yellow	Price
2"	78246	\$40.96



The Brady Boys

- Made of high-impact polyethylene
- Interlocking - no tools or added parts needed
- Weight: 5½ lbs. each
- 41" h x 31" w x 1" thick each
- Standard package: box of two

Catalog #	Legend	Price Each
92270	Caution-Out of Service	\$324.37



Handy Cone™ Floor Signs

- Collapsible, spring-loaded, pyramid-shaped signs set up in seconds
- Stored in a 2" diameter tube
- Standard package: 1 unit

Catalog #	Description	Price Each
47380	31" Warning-People Working	\$68.30
47382	31" Caution -Wet Floor/Piso Mojado	\$68.30
47372	18" Caution -Wet Floor	\$46.82



Bradycone™ Warning System

- Made of high impact, weather-resistant materials
- Easy stacking for storage
- Lock in frame (sold separately) is Black,
- 10" Height, 8¼" x 8¼" face

Catalog #	Description	Price
77203	35" Cone w/ "Safety First" legend	\$78.48
77208	9lbs. Weight Ring	\$37.24
77202	35" Cone w/ "Wet Floor" legend	\$78.24
77204	35" Orange Cone, Blank	\$66.31
77210	Lock-in-Frame	\$14.15



Heavy Duty Floor Stands

- Alert employees and visitors of potential floor hazards
- Made of heavy-duty polypropylene
- Wording appears on both outside panels
- Stand height: 24¾" (closed)
- Standard package: 1 unit

Catalog Number	Legend	Price
104808	Blank	\$43.16
104809	Wet Floor	\$43.16



Reversible Floor Stands

- Alert employees and visitors of potential floor hazards
- Made of lightweight corrugated polypropylene material (B-836)
- Stand size: 12" wide by 20" high (closed)
- Standard package: 1 unit

Cat. No.	Legend	Price
92280	Caution-Slippery When Wet/Wet Floor	\$43.12
92285	Caution-Men Working Above/Below	\$43.12
92281	Caution-Men Working/Hazardous Area	\$43.12



47243

47239

Floor Stands

- Alert employees and visitors of potential floor hazards
- Made of durable Polystyrene Plastic
- Printed with same message on both sides
- Size: 12" wide by 20" high
- Standard package: 1 unit

Catalog Number	Legend	Price
47243	Caution - Tripping Hazard	\$43.51
47239	Danger - Persons Working Above	\$43.51



Identoline® Underground Warning Tape

- Made of heavy-duty B-720 polyethylene
- Tape is 4.0 mil. thick with a tough tensile strength of 1750 psi
- Easily identified - APWA (American Public Works Association) color coding
- Overcoated graphics provide long-lasting legibility and hold color values
- Roll size: 6" x 1,000 ft.
- Standard package: one roll

Catalog Number	Utility Class	APWA Color	Size W X L	Price
91295	Electric*	Red	3" x 1,000'	\$68.88
91296	Electric	Red	6" x 1,000'	\$115.97
91297	Telephone	Orange	6" x 1,000'	\$115.97
91298	Water	Blue	6" x 1,000'	\$115.97

*Legend appears on one line



Detectable Identoline® Warning Tape

- Made of tough B-721 metal detectable polyester
- Subsurface graphics seal the legend from acids, alkalis and other soil substances
- Easily identified - sharply printed legend on APWA color-coded background
- OSHA approved - meets OSHA regulation 1926.956(c)(1) covering location or underground utility lines
- Foil is 4.5 mils
- Standard package: one roll

Catalog Number	Utility Class	APWA Color	Size W X L	Price
91601	Electric	Red	2" x 1,000'	\$158.48
91603	Water	Blue	2" x 1,000'	\$158.48
91600	Gas	Yellow	2" x 1,000'	\$158.48
91606	Fiber Optic	Orange	2" x 1,000'	\$158.48



Marking Flags

- Marking flags are ideal for ground marking
- Flags are 4"H x 5"W and attach to a 30", 15.5 gauge steel rod
- Custom legends available, contact your local Brady distributor for more information
- 100 per package

Cat. No.	Legend	Color	Price
98168	Buried Electric Line	Black/Red	\$27.64

Security Seals

www.BradyID.com

Stock Metal Ball Seals


- Stock Metal Ball Seals are supplied with consecutive numbering (factory chooses starting number) and the word "SEALED" already embossed.
- 100 Seals per package



Catalog #	Description	Price
95197	Metal Ball Seals	\$49.70

Cable Lock Seals

- Heavy steel seals have 12" cable lengths
- The steel head has 6 serialized numbers for inventory or tracking
- Seals have imprinted letters STN.
- Factory chooses the starting number
- 100 per package



Catalog #	Description	Tensile Strength	Price Each
95166	3/16" thick	480 lbs.	\$207.35
95167	3/32" thick	800 lbs.	\$218.67

Pull-Tite Seals

- Deters entry, yet easily removed
- Breaking strength of 10-14 pounds
- Pull-Tite Seals are one of the few security seals approved for use by Underwriter's Laboratories for fire extinguishers and safety doors
- Ideal for use with courier pouches, canisters or cabinets that contain valuables or sensitive documents
- Nine inches long, with ten seals per mat, undercoated Pull-Tite Seals are embossed "SEALED DO NOT REMOVE"
- 100 Seals per package



Description	Catalog #	Price Each
Black	95141	\$92.73
Blue	95143	\$92.73
Green	95144	\$92.73
Orange	95149	\$92.73
Red	95150	\$92.73
Yellow	95155	\$92.73

Stock Plastic Poly-Lok™

- Deters entry, yet easily removed
- Tamper-resistant Poly-Loks are 7 1/2" long, embossed with the wording "Seal", and are consecutively numbered.
- Ships in mats of ten for convenience and better accountability - 100 seals total in package.
- Additional colors are available as a custom order.

Description	Catalog #	Price Each
Blue	95193	\$48.68
Red	95195	\$48.68
Yellow	95196	\$48.68

Simulated Surveillance Camera

- A commercial quality high impact styrene camera housing
- For indoor or outdoor use
- Installs in minutes requiring no wiring


Catalog #	Description	Price Each
95140	Stationary Simulated Surveillance Camera	\$64.34



Deter theft and vandalism. Outwardly, these simulated surveillance cameras are indistinguishable from "live" cameras.

One Step SecurAlert™ Badges



- Pre-assembled for your convenience
- Activated by removing the liner between the “front” badge and the “back” badge
- Contractor and Visitor headers available
- Badges are 2" x 3"
- Badges expire after 24 hours
- 500 front & back badge parts per package




Catalog Number	Description	Price Each
95635	Visitor	\$367.28
95636	Contractor	\$360.15

Self-Expiring Parking Permits

- Temporary parking permits expire during the day by progressively revealing the letters E-X-P-I-R-E-D.
- Expiration process starts once the self-adhesive cover is applied
- Permits are 5" x 3"
- 500 permits per package



Catalog Number	Description	Price Each
95677	Visitor - Red	\$244.59
95678	Visitor - Blue	\$244.59
95679	Visitor - Purple	\$244.59
95680	Temporary - Red	\$244.59
95681	Temporary - Blue	\$244.59
95682	Temporary - Purple	\$244.59



Retractable Badge Holder

- Attach to belt or clothing
- Retractable Badge Holder with clip is the ideal alternative to bull dog clips which may damage clothing
- Clip attaches to belt or pocket while the heavy-duty nylon cable with fastener attaches to badge

Catalog Number	Color	Price Each
95071	Blue	\$10.69
95073	White	\$10.69
95074	Gray	\$10.69
95075	Black	\$10.69



Badge retracts when released shown with Custom Plastic Badge

Dispensers

www.BradyID.com

Dispensers



PPE Dispenser

- Store bouffants, booties, gloves, ear plugs, etc. and pull it out from the 4" round opening
- Wall or table mount
- Dispenser Dimensions: 10"H x 10"W x 10"D

Catalog #	Description	Price
DPE	PPE Dispenser	\$70.69



Miscellaneous PPE Dispenser

- Foam bottom
- Wall or table mount
- Size: 9¹/₂"H x 11¹/₂"W x 9¹/₂"D

Catalog #	Description	Price
MPPE	Misc. PPE Dispenser	\$67.33



Head Wear Dispensers

- Middle divider makes it easy to separate
- White acrylic with see-through lid
- Table top only
- Size: 11¹/₂"H x 15³/₈"W x 9"D

Catalog #	Description	Price
*PD240E	Hairnets	\$87.53



Head Wear Dispensers

- Middle divider makes it easy to separate
- White acrylic with see-through lid
- Table top only
- Size: 11¹/₂"H x 15³/₈"W x 9"D

Catalog #	Description	Price
PD241E	'Sanitary Headwear'	\$121.14



Bouffant Cap / Beard

- Table or wall mount for easy access
- Size: 14"H x 12"W x 8"D

Catalog #	Description	Price
PD524E	Bouffant Cap Dispenser	\$94.72
PD325E	Beard Cover Dispenser	\$94.72



Dust Mask Dispenser

- Unique cutout design that allows you to reach in the opening to easily remove
- Holds more than 30 masks
- Size: 12¹/₂"H x 6"W x 6"D

Catalog #	Description	Price
M420	Dust Mask Dispenser	\$72.00



Glove Dispensers

- The single, double and triple units are all vertically mounted on either wall or counter

Catalog #	Desc.	Size (HxWxD)	Price
GD01	Single	5" x 10.93" x 4.12"	\$33.70
GD02	Double	10" x 10.375" x 4.12"	\$46.35
GD03	Triple	15" x 10.375" x 4.12"	\$52.76



Deluxe Glove Dispenser

- The deluxe triple is mounted horizontally and allows you to change one box without affecting the others
- Size: 11¹³/₁₆"H x 20"W x 4"D

Catalog #	Description	Price
GD03DL	Deluxe Glove Dispenser	\$95.76



Deluxe Visitor Spec

- Each dispensers holds approx. 20-25 glasses
- Wall mount only
- Size: 18"H x 8"W x 4"D

Catalog #	Description	Price
MVSD	Deluxe Visitor Spec Dispenser	\$72.71
MVSDL	Deluxe w/cover (not shown)	\$76.41
EHMVSD	Economy Dispenser (17 ³ / ₄ "x8"x4")	\$67.66



Large Capacity Eye Protection Dispenser

- Clear acrylic unit can be wall or table mounted
- Holds approximately 35 pairs
- Size: 12 1/4"H x 18"W x 9 1/4"D

Catalog #	Description	Price
PD701E	Dispenser	\$127.19



Large Capacity Ear Plug Dispenser

- Removable inner slanted shelf
- Holds a standard box of 200 disposables
- Size: 13"H x 12"W x 8"D
- Wall or table mount

Catalog #	Description	Price
PD439G	Dispenser	\$89.24



Compact Ear Plug Dispenser

- Cushioned foam bottom
- Wall or table mount
- Size: 3"H x 9"W x 6"D with 6" high backplate

Catalog #	Description	Price
2019L	Dispenser	\$47.37
2019	Dispenser w/o cover	\$33.82



Safety Glasses Holder

- This compact unit holds 4-6 pairs of glasses
- Wall or table mount
- Size: 3"H x 9"W x 6"D with 6" high back plate

Catalog #	Description	Price
2011L	Holder	\$47.37
2011	Holder w/o Cover	\$33.82



Ear Plug Dispenser

- Holds 100 to 150 pairs
- Wall or table mount
- Dispenser size: 13"H x 6"W x 8"D

Catalog #	Description	Price
EPD	Ear Plug Tray	\$70.35



Clear Acrylic Dispenser Tray

- Use on tabletop or mount on wall
- Size: 3"H x 9"W x 6"D with 6" backplate

Catalog #	Description	Price
PD205A	Dispenser tray	\$33.15
PD206A	Tray with lid (not shown)	\$46.69



Double Bottle Eye Wash Station

- Proper usage instructions silk-screened on door
- Wall or table mount
- Size: 10"H x 10 1/4"W x 7"D

Catalog #	Description	Price
PD997E	Double Bottle	\$82.53
PD995E	Single Bottle (6 1/4" W)	\$62.42



Divided Hearing Protection Dispenser

- Use two different kinds of hearing protection.
- Table top use only
- Dispenser size: 11 1/2"H x 15 3/8"W x 9"D

Catalog #	Description	Price
PD265E	Divided Hearing Protection	\$121.71



Shoe Cover Dispenser

- Holds over 50 pairs of poly shoe covers
- Table top or wall mount
- Size: 14"H x 12"W x 8"D

Catalog #	Description	Price
PD322E	Shoe Cover Dispenser	\$94.25

BMP®71 Label Printer

www.BradyID.com/bmp71

Sign And Label Printers

NEW!

BMP®71
LABEL PRINTER

Thousands Of Applications.
Hundreds Of Labels.
One Label Printer.



The one way
to faster,
easier label
printing.



Electrical Labeling



Voice/Data Comm Labeling



Safety Labels



PermaSleeve™ Markers



Self-Laminating Labels



General ID Labels

...and many more.

The best features and functionalities of Brady's portable label printers are now combined into one easy-to-use, top-of-the-line portable thermal transfer printer – Brady's NEW BMP®71 printer. Whether you need ¼" self-laminating wire marker labels or 2" wide vinyl pipe marker labels, you only need ONE label maker - the BMP®71 printer can do it all!



Online Video:
www.BradyID.com/bmp71

Features include:

- 100's Of Symbols
- Reverse Print
- Multiple Font Size
- Subscripts
- Frame
- Mirror Print
- Color Screen
- Auto Font Size
- Vertical
- Expand/Condense
- Time/Date Stamps
- Underline/Italics/Bold
- Barcodes
- Serialization



Did You Know?

The BMP®71 Label Printer can also print on TLS2200® Consumables and HandiMark® Consumables using the included Media Adaptor!

Catalog Number	Description	Price Each
BMP71*	BMP71 Label Printer	\$895.00
BMP71-LM*	BMP71 Label Printer with LabelMark Software	\$984.60
BMP71-MW*	BMP71 Label Printer with Markware Lean Software	\$1344.60
BMP71-QC*	BMP71 Label Printer with Quick Charger	\$955.00
BMP71-SC*	BMP71 Label Printer with Soft Case	\$920.00
BMP71-SC-QC*	BMP71 Label Printer with Soft Case and Quick Charger	\$980.00
M71-AC-BC	BMP71 AC/Battery Adaptor	\$59.00
M71-ADAPT	TLS/Handimark Media Adaptor	\$19.50
M71-BATT	BMP71 Battery Pack	\$85.00
M71-CABLE	BMP71 USB Cable	\$16.95
M71-CLEAN	BMP71 Cleaning Kit	\$15.00
M71-HC	BMP71 Hardcase	\$75.00
M71-QC	BMP71 Quick Charger	\$115.00
M71-SC	BMP71 Softcase	\$45.00
BMP71-360	Brady360® Replacement Printer Program	\$179.00
BMP71-360-KIT	BMP71 Label Printer and Brady360® Replacement Printer Program	\$1074.00

*Label printer ships with Hardcase, Charger/AC Adapter, 1 Roll of M71-31-423 White Die Cut Labels, 1 M71-R6000 Black Ribbon Cartridge, M71-ADAPT Roll Adapter, USB Cable, Quickstart Guide, a CD including the Printer Driver, Users Guide and Tutorial. Pat. No. 7,999,836

Brady 360® Replacement Printer Plan

The Brady 360™ Printer Replacement Plan supplements the Limited Warranty already provided to you with the purchase of your Brady printer. With this plan, Brady Worldwide Inc., in its reasonable discretion, will send a replacement printer in the event that your covered printer requires service during the term of its Limited Warranty. Brady will replace your defective printer with a new printer that has the same or similar functionality and is of the same or greater value.

Limit two new replacement printers per covered printer in each warranty period. The plan must be purchased at the time of printer purchase to be valid.

** Limit of two printers in the first 12 months of initial purchase.

General Industrial, Lean & Safety

Indoor/outdoor pliable vinyl conforms to smooth or rough surfaces such as pipes, walls, doors, panels, shelving, bins, and equipment. Aggressive permanent adhesive; labels offer excellent resistance to oils, detergents, dirt, grime, and many solvents.

Note: As of March 2011, B-580 material has been replaced by B-595 material. The updated part numbers are shown in table below.

For example: part number "M71C-500-580-BK" has become "M71C-500-595-BK"




Figure 8



Indoor/Outdoor Grade Vinyl Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)		Recommended Ribbon	Price
						B Inch	(mm)		
Fig. 8	M71C-500-595-BK	1 Roll (cont.)	B-595	Black	0.500	(12.700)	50 ft. (15.24 m)	M71-R4400-WT	\$47.22
Fig. 8	M71C-500-595-BL	1 Roll (cont.)	B-595	Blue	0.500	(12.700)	50 ft. (15.24 m)	M71-R4400-WT	\$47.22
Fig. 8	M71C-500-595-BR	1 Roll (cont.)	B-595	Brown	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-CL	1 Roll (cont.)	B-595	Clear	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-GD	1 Roll (cont.)	B-595	Gold	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-GN	1 Roll (cont.)	B-595	Green	0.500	(12.700)	50 ft. (15.24 m)	M71-R4400-WT	\$47.22
Fig. 8	M71C-500-595-GY	1 Roll (cont.)	B-595	Grey	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-LB	1 Roll (cont.)	B-595	Light Blue	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-OC	1 Roll (cont.)	B-595	Ochre	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-OR	1 Roll (cont.)	B-595	Orange	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-PK	1 Roll (cont.)	B-595	Pink	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-PL	1 Roll (cont.)	B-595	Purple	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-RD	1 Roll (cont.)	B-595	Red	0.500	(12.700)	50 ft. (15.24 m)	M71-R4400-WT	\$47.22
Fig. 8	M71C-500-595-SB	1 Roll (cont.)	B-595	Sky Blue	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-TN	1 Roll (cont.)	B-595	Tan	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-WT	1 Roll (cont.)	B-595	White	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-500-595-YL	1 Roll (cont.)	B-595	Yellow	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$47.22
Fig. 8	M71C-1000-595-BK	1 Roll (cont.)	B-595	Black	1.000	(25.400)	50 ft. (15.24 m)	M71-R4400-WT	\$65.87
Fig. 8	M71C-1000-595-BL	1 Roll (cont.)	B-595	Blue	1.000	(25.400)	50 ft. (15.24 m)	M71-R4400-WT	\$65.87
Fig. 8	M71C-1000-595-BR	1 Roll (cont.)	B-595	Brown	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-CL	1 Roll (cont.)	B-595	Clear	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-GD	1 Roll (cont.)	B-595	Gold	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-GN	1 Roll (cont.)	B-595	Green	1.000	(25.400)	50 ft. (15.24 m)	M71-R4400-WT	\$65.87
Fig. 8	M71C-1000-595-GY	1 Roll (cont.)	B-595	Grey	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-LB	1 Roll (cont.)	B-595	Light Blue	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-OC	1 Roll (cont.)	B-595	Ochre	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-OR	1 Roll (cont.)	B-595	Orange	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-PK	1 Roll (cont.)	B-595	Pink	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-PL	1 Roll (cont.)	B-595	Purple	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-RD	1 Roll (cont.)	B-595	Red	1.000	(25.400)	50 ft. (15.24 m)	M71-R4400-WT	\$65.87
Fig. 8	M71C-1000-595-SB	1 Roll (cont.)	B-595	Sky Blue	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-TN	1 Roll (cont.)	B-595	Tan	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-WT	1 Roll (cont.)	B-595	White	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-1000-595-YL	1 Roll (cont.)	B-595	Yellow	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$65.87
Fig. 8	M71C-2000-595-BK	1 Roll (cont.)	B-595	Black	2.000	(50.800)	50 ft. (15.24 m)	M71-R4400-WT	\$98.85
Fig. 8	M71C-2000-595-BL	1 Roll (cont.)	B-595	Blue	2.000	(50.800)	50 ft. (15.24 m)	M71-R4400-WT	\$98.85
Fig. 8	M71C-2000-595-BR	1 Roll (cont.)	B-595	Brown	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-CL	1 Roll (cont.)	B-595	Clear	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-GD	1 Roll (cont.)	B-595	Gold	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-GN	1 Roll (cont.)	B-595	Green	2.000	(50.800)	50 ft. (15.24 m)	M71-R4400-WT	\$98.85
Fig. 8	M71C-2000-595-GY	1 Roll (cont.)	B-595	Grey	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-LB	1 Roll (cont.)	B-595	Light Blue	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-OC	1 Roll (cont.)	B-595	Ochre	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-OR	1 Roll (cont.)	B-595	Orange	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-PK	1 Roll (cont.)	B-595	Pink	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-PL	1 Roll (cont.)	B-595	Purple	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-RD	1 Roll (cont.)	B-595	Red	2.000	(50.800)	50 ft. (15.24 m)	M71-R4400-WT	\$98.85
Fig. 8	M71C-2000-595-SB	1 Roll (cont.)	B-595	Sky Blue	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-TN	1 Roll (cont.)	B-595	Tan	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-WT	1 Roll (cont.)	B-595	White	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85
Fig. 8	M71C-2000-595-YL	1 Roll (cont.)	B-595	Yellow	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$98.85

* See all ribbon colors on page 115.

BMP®71 Label Printer Materials

www.BradyID.com/bmp71

Sign And Label Printers

General Industrial, Lean & Safety (Continued)

Pre-Printed Die Cut Labels




Figure 4




Figure 8




Figure 27




Figure 28




Figure 30

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions			Recommended Ribbon	Price
					A Inch	B Inch	(mm)		
Fig. 28	M71-30-423-TEST	250	B-423	White	1.500	0.750	(38.100) (19.050)	M71-R6000	\$38.71
Fig. 27	M71-30-428-CALI	250	B-428	White	1.500	0.750	(38.100) (19.050)	M71-R4300	\$59.91
Fig. 30	M71-35-428-PROP	250	B-428	White	1.630	0.750	(41.400) (19.050)	M71-R4300	\$59.91
Fig. 4	M71-38-483-CAUT	100	B-483	White	4.000	1.900	(101.600) (48.260)	M71-R6000	\$58.04
Fig. 4	M71-38-483-DANG	100	B-483	White	4.000	1.900	(101.600) (48.260)	M71-R6000	\$58.04
Fig. 4	M71-38-483-NOTI	100	B-483	White	4.000	1.900	(101.600) (48.260)	M71-R6000	\$58.04
Fig. 4	M71-38-483-WARN	100	B-483	White	4.000	1.900	(101.600) (48.260)	M71-R6000	\$58.04

Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions			Recommended Ribbon	Price
					A Inch	B Inch	(mm)		
Fig. 8	M71C-500-428	1 Roll (cont.)	B-428	Silver	0.500	50 ft.	(12.700) (15.240 m)	M71-R4300	\$62.48
Fig. 8	M71C-1000-529	1 Roll (cont.)	B-529	White	1.000	50 ft.	(25.400) (15.240 m)	M71-R6000	\$51.79
Fig. 8	M71C-2000-529	1 Roll (cont.)	B-529	White	2.000	50 ft.	(50.800) (15.240 m)	M71-R6000	\$71.97

Control Panel/Raised Panel

Customized legend plates with less hassle and wasted time than engraved plates. Brady Raised Panel Labels are RoHS compliant and UL approved. Aggressive adhesive and solvent resistant makes them a great replacement for engraved tags.




Figure 4




Figure 25




Diagram	Part Number	Labels/Roll	Material	Color	Label Dimensions			Recommended Ribbon	Price
					A Inch (mm)	B Inch (mm)	C Inch (mm)		
Fig. 4	M71EP-171-593	200	B-593	White	1.060 (26.920)	0.490 (12.450)	-	M71-R6000	\$104.95
Fig. 4	M71EP-171-593-BK	200	B-593	Black	1.060 (26.920)	0.490 (12.450)	-	M71-R4400-WT	\$104.95
Fig. 4	M71EP-171-593-GN	200	B-593	Green	1.060 (26.920)	0.490 (12.450)	-	M71-R4400-WT	\$104.95
Fig. 4	M71EP-171-593-RD	200	B-593	Red	1.060 (26.920)	0.490 (12.450)	-	M71-R4400-WT	\$104.95
Fig. 4	M71EP-171-593-SL	200	B-593	Silver	1.060 (26.920)	0.490 (12.450)	-	M71-R6000	\$104.95
Fig. 4	M71EP-171-593-YL	200	B-593	Yellow	1.060 (26.920)	0.490 (12.450)	-	M71-R6000	\$104.95
Fig. 25	M71EP-167-593	100	B-593	White	1.200 (30.480)	1.500 (38.100)	0.890 (22.500)	M71-R6000	\$94.45
Fig. 25	M71EP-167-593-BK	100	B-593	Black	1.200 (30.480)	1.500 (38.100)	0.890 (22.500)	M71-R4400-WT	\$94.45
Fig. 25	M71EP-167-593-GN	100	B-593	Green	1.200 (30.480)	1.500 (38.100)	0.890 (22.500)	M71-R4400-WT	\$94.45
Fig. 25	M71EP-167-593-RD	100	B-593	Red	1.200 (30.480)	1.500 (38.100)	0.890 (22.500)	M71-R4400-WT	\$94.45
Fig. 25	M71EP-167-593-YL	100	B-593	Yellow	1.200 (30.480)	1.500 (38.100)	0.890 (22.500)	M71-R6000	\$94.45
Fig. 25	M71EP-168-593	100	B-593	White	1.200 (30.480)	1.900 (48.260)	0.890 (22.500)	M71-R6000	\$104.95
Fig. 25	M71EP-168-593-BK	100	B-593	Black	1.200 (30.480)	1.900 (48.260)	0.890 (22.500)	M71-R4400-WT	\$104.95
Fig. 25	M71EP-168-593-GN	100	B-593	Green	1.200 (30.480)	1.900 (48.260)	0.890 (22.500)	M71-R4400-WT	\$104.95
Fig. 25	M71EP-168-593-RD	100	B-593	Red	1.200 (30.480)	1.900 (48.260)	0.890 (22.500)	M71-R4400-WT	\$104.95
Fig. 25	M71EP-168-593-YL	100	B-593	Yellow	1.200 (30.480)	1.900 (48.260)	0.890 (22.500)	M71-R6000	\$104.95
Fig. 25	M71EP-169-593	100	B-593	White	1.800 (45.720)	1.800 (45.720)	1.200 (30.500)	M71-R6000	\$111.25
Fig. 25	M71EP-169-593-BK	100	B-593	Black	1.800 (45.720)	1.800 (45.720)	1.200 (30.500)	M71-R4400-WT	\$111.25
Fig. 25	M71EP-169-593-GN	100	B-593	Green	1.800 (45.720)	1.800 (45.720)	1.200 (30.500)	M71-R4400-WT	\$111.25
Fig. 25	M71EP-169-593-RD	100	B-593	Red	1.800 (45.720)	1.800 (45.720)	1.200 (30.500)	M71-R4400-WT	\$111.25
Fig. 25	M71EP-169-593-YL	100	B-593	Yellow	1.800 (45.720)	1.800 (45.720)	1.200 (30.500)	M71-R6000	\$111.25
Fig. 4	M71EP-173-593	100	B-593	White	2.000 (50.800)	1.000 (25.400)	-	M71-R6000	\$79.75
Fig. 4	M71EP-173-593-BK	100	B-593	Black	2.000 (50.800)	1.000 (25.400)	-	M71-R4400-WT	\$79.75
Fig. 4	M71EP-173-593-GN	100	B-593	Green	2.000 (50.800)	1.000 (25.400)	-	M71-R4400-WT	\$79.75
Fig. 4	M71EP-173-593-RD	100	B-593	Red	2.000 (50.800)	1.000 (25.400)	-	M71-R4400-WT	\$79.75
Fig. 4	M71EP-173-593-SL	100	B-593	Silver	2.000 (50.800)	1.000 (25.400)	-	M71-R6000	\$79.75
Fig. 4	M71EP-173-593-YL	100	B-593	Yellow	2.000 (50.800)	1.000 (25.400)	-	M71-R6000	\$79.75
Fig. 4	M71EP-176-593	50	B-593	White	3.000 (76.200)	1.000 (25.400)	-	M71-R6000	\$62.95
Fig. 4	M71EP-176-593-BK	50	B-593	Black	3.000 (76.200)	1.000 (25.400)	-	M71-R4400-WT	\$62.95
Fig. 4	M71EP-176-593-GN	50	B-593	Green	3.000 (76.200)	1.000 (25.400)	-	M71-R4400-WT	\$62.95
Fig. 4	M71EP-176-593-RD	50	B-593	Red	3.000 (76.200)	1.000 (25.400)	-	M71-R4400-WT	\$62.95
Fig. 4	M71EP-176-593-YL	50	B-593	Yellow	3.000 (76.200)	1.000 (25.400)	-	M71-R6000	\$62.95
Fig. 4	M71EP-174-593	50	B-593	White	4.000 (101.600)	1.000 (25.400)	-	M71-R6000	\$79.75
Fig. 4	M71EP-174-593-BK	50	B-593	Black	4.000 (101.600)	1.000 (25.400)	-	M71-R4400-WT	\$79.75
Fig. 4	M71EP-174-593-GN	50	B-593	Green	4.000 (101.600)	1.000 (25.400)	-	M71-R4400-WT	\$79.75
Fig. 4	M71EP-174-593-RD	50	B-593	Red	4.000 (101.600)	1.000 (25.400)	-	M71-R4400-WT	\$79.75
Fig. 4	M71EP-174-593-SL	50	B-593	Silver	4.000 (101.600)	1.000 (25.400)	-	M71-R6000	\$79.75
Fig. 4	M71EP-174-593-YL	50	B-593	Yellow	4.000 (101.600)	1.000 (25.400)	-	M71-R6000	\$79.75

See all ribbon colors on page 115.

General Labels/Rating Plates

Choose from several materials with aggressive adhesives for use in commercial/industrial applications.




Die Cut Labels

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch	Recommended (mm)	Ribbon	Price
Fig. 4	M71-68-430	750	B-430	Clear	0.240	(6.000)	0.150	(3.810)	M71-R6000	\$32.64
Fig. 4	M71-71-430	750	B-430	Clear	0.350	(8.890)	0.200	(5.080)	M71-R6000	\$32.64
Fig. 14	M71-80-488	250	B-488	White	0.750	(19.050)	0.900	(22.860)	M71-R4300	\$26.57
Fig. 4	M71-97-488	250	B-488	White	0.900	(22.860)	0.900	(22.860)	M71-R4300	\$28.92
Fig. 4	M71-16-430	500	B-430	Clear	1.000	(25.400)	0.375	(9.530)	M71-R6000	\$46.65
Fig. 4	M71-17-430	500	B-430	Clear	1.000	(25.400)	0.500	(12.700)	M71-R6000	\$46.65
Fig. 4	M71-16-483	500	B-483	White	1.000	(25.400)	0.375	(9.530)	M71-R6000	\$51.68
Fig. 4	M71-17-483	500	B-483	White	1.000	(25.400)	0.500	(12.700)	M71-R6000	\$52.73
Fig. 4	M71-19-483	250	B-483	White	1.000	(25.400)	1.000	(25.400)	M71-R6000	\$37.13
Fig. 4	M71-17-486	500	B-486	Silver	1.000	(25.400)	0.500	(12.700)	M71-R4300	\$58.75
Fig. 4	M71-45-430	500	B-430	Clear	1.050	(38.100)	0.375	(9.530)	M71-R6000	\$48.75
Fig. 4	M71-65-483	250	B-483	White	1.375	(34.930)	1.000	(25.400)	M71-R6000	\$32.90
Fig. 4	M71-29-459	500	B-459	White	1.500	(38.100)	0.500	(12.700)	M71-R6000	\$47.42
Fig. 4	M71-30-459	250	B-459	White	1.500	(38.100)	0.750	(19.050)	M71-R6000	\$41.49
Fig. 4	M71-29-483	500	B-483	White	1.500	(38.100)	0.500	(12.700)	M71-R6000	\$58.53
Fig. 4	M71-30-483	250	B-483	White	1.500	(38.100)	0.750	(19.050)	M71-R6000	\$50.33
Fig. 4	M71-31-483	250	B-483	White	1.500	(38.100)	1.000	(25.400)	M71-R6000	\$42.01
Fig. 4	M71-29-486	500	B-486	Silver	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$67.60
Fig. 4	M71-30-486	250	B-486	Silver	1.500	(38.100)	0.750	(19.050)	M71-R4300	\$55.41
Fig. 4	M71-29-489	500	B-489	White	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$57.60
Fig. 4	M71-32-489	250	B-489	White	1.500	(38.100)	1.500	(38.100)	M71-R4300	\$58.80
Fig. 4	M71-81-488	750	B-488	White	1.900	(48.260)	0.250	(6.350)	M71-R4300	\$65.81
Fig. 4	M71-20-459	100	B-459	White	2.000	(50.800)	1.000	(25.400)	M71-R6000	\$25.36
Fig. 4	M71-61-483	100	B-483	White	2.000	(50.800)	0.500	(12.700)	M71-R6000	\$18.88
Fig. 4	M71-20-483	100	B-483	White	2.000	(50.800)	1.000	(25.400)	M71-R6000	\$28.69
Fig. 4	M71-20-486	100	B-486	Silver	2.000	(50.800)	1.000	(25.400)	M71-R4300	\$36.05
Fig. 4	M71-37-483	100	B-483	White	3.000	(76.200)	1.900	(48.260)	M71-R6000	\$42.01
Fig. 4	M71-37-486	100	B-486	Silver	3.000	(76.200)	1.900	(48.260)	M71-R4300	\$51.96
Fig. 4	M71-23-483	100	B-483	White	4.000	(101.600)	1.000	(25.400)	M71-R6000	\$43.37
Fig. 4	M71-38-483	100	B-483	White	4.000	(101.600)	1.900	(48.260)	M71-R6000	\$50.47
Fig. 4	M71-38-489	100	B-489	White	4.000	(101.600)	1.900	(48.260)	M71-R4300	\$50.47

Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch (mm)	Recommended Ribbon	Price
Fig. 8	M71C-375-430	1 Roll (cont.)	B-430	Clear	0.375	(9.530)	50 ft. (15.24 m)	M71-R6000	\$54.57
Fig. 8	M71C-500-430	1 Roll (cont.)	B-430	Clear	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$54.57
Fig. 8	M71C-500-483	1 Roll (cont.)	B-483	White	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$61.58
Fig. 8	M71C-1000-430	1 Roll (cont.)	B-430	Clear	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$75.31
Fig. 8	M71C-1000-483	1 Roll (cont.)	B-483	White	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$85.22
Fig. 8	M71C-1900-430	1 Roll (cont.)	B-430	Clear	1.900	(48.260)	50 ft. (15.24 m)	M71-R6000	\$112.71
Fig. 8	M71C-1900-483	1 Roll (cont.)	B-483	White	1.900	(48.260)	50 ft. (15.24 m)	M71-R6000	\$126.97

See all ribbon colors on page 115.



BMP[®]71 Label Printer Materials

www.BradyID.com/bmp71

Sign And Label Printers

Circuit Board & Component ID

Various sizes and label types for marking relays, solenoids, switches, drive motors, and other components.




Figure 4



Figure 8



Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions			Recommended Ribbon	Price
						(mm)	B Inch	(mm)		
Fig. 8	M71C-500-423	1 Roll (cont.)	B-423	White	0.500	(12.700)	50 ft.	(15.24 m)	M71-R6000	\$49.55

Die Cut Labels


Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions			Recommended Ribbon	Price
						(mm)	B Inch	(mm)		
Fig. 4	M71-1-423	750	B-423	White	0.250	(6.350)	0.250	(6.350)	M71-R6000	\$27.37
Fig. 4	M71-3-423	500	B-423	White	0.375	(9.530)	0.375	(9.530)	M71-R6000	\$28.54
Fig. 4	M71-3-457	500	B-457	White	0.375	(9.530)	0.375	(9.530)	M71-R6000	\$97.10
Fig. 4	M71-4-423	500	B-423	White	0.400	(10.160)	0.400	(10.160)	M71-R6000	\$29.87
Fig. 4	M71-5-423	750	B-423	White	0.500	(12.700)	0.200	(5.080)	M71-R6000	\$38.71
Fig. 4	M71-6-423	750	B-423	White	0.500	(12.700)	0.280	(6.990)	M71-R6000	\$40.71
Fig. 4	BM71-7-423*	5000	B-423	White	0.500	(12.700)	0.500	(12.700)	M71-R6000	\$300.36
Fig. 4	M71-7-423	500	B-423	White	0.500	(12.700)	0.500	(12.700)	M71-R6000	\$35.85
Fig. 4	M71-6-473	750	B-473	White	0.500	(12.700)	0.275	(6.990)	M71-R6000	\$51.78
Fig. 4	M71-9-423	750	B-423	White	0.650	(16.510)	0.200	(5.080)	M71-R6000	\$42.95
Fig. 4	M71-9-426	750	B-426	Amber	0.650	(16.510)	0.200	(5.080)	M71-R4300	\$145.50
Fig. 4	M71-9-473	750	B-473	White	0.650	(16.510)	0.200	(5.080)	M71-R6000	\$53.79
Fig. 4	M71-10-457	750	B-457	White	0.750	(19.050)	0.250	(6.350)	M71-R6000	\$147.14
Fig. 4	M71-10-473	750	B-473	White	0.750	(19.050)	0.250	(6.350)	M71-R6000	\$55.36
Fig. 4	M71-10-423	750	B-423	White	0.750	(19.050)	0.250	(6.350)	M71-R6000	\$44.27
Fig. 4	M71-13-423	750	B-423	White	0.900	(22.860)	0.250	(6.350)	M71-R6000	\$47.17
Fig. 4	M71-13-426	750	B-426	Amber	0.900	(22.860)	0.250	(6.350)	M71-R4300	\$142.65
Fig. 4	M71-14-423	750	B-423	White	1.000	(25.400)	0.187	(4.750)	M71-R6000	\$50.06
Fig. 4	M71-15-423	750	B-423	White	1.000	(25.400)	0.275	(6.990)	M71-R6000	\$51.52
Fig. 4	BM71-16-423*	5000	B-423	White	1.000	(25.400)	0.375	(9.530)	M71-R6000	\$297.41
Fig. 4	M71-16-423	500	B-423	White	1.000	(25.400)	0.375	(9.530)	M71-R6000	\$42.41
Fig. 4	BM71-17-423*	5000	B-423	White	1.000	(25.400)	0.500	(12.700)	M71-R6000	\$288.69
Fig. 4	M71-17-423	500	B-423	White	1.000	(25.400)	0.500	(12.700)	M71-R6000	\$42.41
Fig. 4	BM71-19-423*	2500	B-423	White	1.000	(25.400)	1.000	(25.400)	M71-R6000	\$209.69
Fig. 4	M71-19-423	250	B-423	White	1.000	(25.400)	1.000	(25.400)	M71-R6000	\$29.99
Fig. 4	M71-16-426	500	B-426	Amber	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$159.57
Fig. 4	M71-17-426	500	B-426	Amber	1.000	(25.400)	0.500	(12.700)	M71-R4300	\$163.68
Fig. 4	M71-15-428	750	B-428	Silver	1.000	(25.400)	0.275	(6.990)	M71-R4300	\$66.68
Fig. 4	BM71-17-428*	5000	B-428	Silver	1.000	(25.400)	0.500	(12.700)	M71-R4300	\$375.47
Fig. 4	M71-17-428	500	B-428	Silver	1.000	(25.400)	0.500	(12.700)	M71-R4300	\$53.62
Fig. 4	M71-16-457	500	B-457	White	1.000	(25.400)	0.375	(9.530)	M71-R6000	\$159.57
Fig. 4	M71-16-473	500	B-473	White	1.000	(25.400)	0.375	(9.530)	M71-R6000	\$53.13
Fig. 4	M71-17-473	500	B-473	White	1.000	(25.400)	0.500	(12.700)	M71-R6000	\$53.13
Fig. 4	M71-24-423-BK	500	B-423	Black	1.130	(28.700)	0.500	(12.700)	M71-R6000	\$41.23
Fig. 4	M71-25-423	750	B-423	White	1.250	(31.750)	0.250	(6.350)	M71-R6000	\$54.31
Fig. 4	M71-27-423	750	B-423	White	1.500	(38.100)	0.125	(3.180)	M71-R6000	\$55.50
Fig. 4	M71-28-423	750	B-423	White	1.500	(38.100)	0.250	(6.350)	M71-R6000	\$61.83
Fig. 4	BM71-29-423*	5000	B-423	White	1.500	(38.100)	0.500	(12.700)	M71-R6000	\$331.92
Fig. 4	M71-29-423	500	B-423	White	1.500	(38.100)	0.500	(12.700)	M71-R6000	\$47.42
Fig. 4	M71-31-423	250	B-423	White	1.500	(38.100)	1.000	(25.400)	M71-R6000	\$34.09
Fig. 4	M71-32-423	250	B-423	White	1.500	(38.100)	1.500	(38.100)	M71-R6000	\$48.49
Fig. 4	M71-28-426	750	B-426	Amber	1.500	(38.100)	0.250	(6.350)	M71-R4300	\$187.43
Fig. 4	M71-29-428	500	B-428	Silver	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$61.70
Fig. 4	M71-28-473	750	B-473	White	1.500	(38.100)	0.250	(6.350)	M71-R6000	\$77.19
Fig. 4	M71-2-423	100	B-423	White	2.000	(50.800)	0.250	(6.350)	M71-R6000	\$18.35
Fig. 4	BM71-20-423*	1000	B-423	White	2.000	(50.800)	1.000	(25.400)	M71-R6000	\$167.42
Fig. 4	M71-20-423	100	B-423	White	2.000	(50.800)	1.000	(25.400)	M71-R6000	\$23.91
Fig. 4	BM71-20-424*	1000	B-424	White	2.000	(50.800)	1.000	(25.400)	M71-R4300	\$193.42
Fig. 4	M71-20-424	100	B-424	White	2.000	(50.800)	1.000	(25.400)	M71-R4300	\$18.24
Fig. 4	BM71-20-428*	1000	B-428	Silver	2.000	(50.800)	1.000	(25.400)	M71-R4300	\$34.74
Fig. 4	M71-20-428	100	B-428	Silver	2.000	(50.800)	1.000	(25.400)	M71-R4300	\$32.84
Fig. 4	M71-26-423	100	B-423	White	2.750	(69.850)	1.250	(31.750)	M71-R6000	\$34.74
Fig. 4	M71-26-428	100	B-428	White	2.750	(69.850)	1.250	(31.750)	M71-R4300	\$47.33
Fig. 4	M71-22-423	100	B-423	White	3.000	(76.200)	1.000	(25.400)	M71-R6000	\$28.81
Fig. 4	M71-37-423	100	B-423	White	3.000	(76.200)	1.900	(48.260)	M71-R6000	\$34.74
Fig. 4	M71-22-428	100	B-428	Silver	3.000	(76.200)	1.000	(25.400)	M71-R4300	\$39.39
Fig. 4	M71-23-423	100	B-423	White	4.000	(101.600)	1.000	(25.400)	M71-R6000	\$34.74
Fig. 4	M71-38-423	100	B-423	White	4.000	(101.600)	1.900	(48.260)	M71-R6000	\$41.49
Fig. 4	M71-38-428	100	B-428	White	4.000	(101.600)	1.900	(48.260)	M71-R4300	\$52.47

* "B" indicates bulk roll.

See all ribbon colors on page 115.

Wire And Cable Markers

Durable vinyl cloth wrap around wire and cable markers.
Firm adhesive can be removed cleanly and reapplied.




Wrap Around Wire ID Labels

Diagram	Part Number	Labels/Roll	Material	Color	Approx. Wire Gauge	A Inch	Label Dimensions (mm)		Recommended Ribbon	Price
							B Inch			
Fig. 6	M71-21-499	100	B-499	White	Cables	1.000	2.500	(63.500)	M71-R4300	\$38.74
Fig. 6	M71-21-498	100	B-498	White	Cables	1.000	2.500	(63.500)	M71-R6200	\$32.84
Fig. 6	M71-33-498	100	B-498	White	Cables	1.500	4.000	(101.600)	M71-R6200	\$53.88
Fig. 6	M71-10-498	750	B-498	White	16-10	0.250	0.750	(19.050)	M71-R6200	\$51.20
Fig. 12	M71-7-499	500	B-499	White	16-10	0.500	0.500	(12.700)	M71-R4300	\$50.25
Fig. 12	M71-7-498	500	B-498	White	16-10	0.500	0.500	(12.700)	M71-R6200	\$49.28
Fig. 6	BM71-11-499*	5000	B-499	White	16-10	0.500	0.750	(19.050)	M71-R4300	\$321.24
Fig. 6	M71-11-499	500	B-499	White	16-10	0.500	0.750	(19.050)	M71-R4300	\$45.80
Fig. 6	BM71-11-498*	5000	B-498	White	16-10	0.500	0.750	(19.050)	M71-R6200	\$313.52
Fig. 6	M71-11-498	500	B-498	White	16-10	0.500	0.750	(19.050)	M71-R6200	\$44.76
Fig. 6	M71-16-499	500	B-499	White	12-10	0.375	1.000	(25.400)	M71-R4300	\$54.96
Fig. 6	M71-16-498	500	B-498	White	12-10	0.375	1.000	(25.400)	M71-R6200	\$53.78
Fig. 6	M71-18-499	250	B-499	White	12-10	0.750	1.000	(25.400)	M71-R4300	\$37.82
Fig. 6	BM71-18-498*	2500	B-498	White	12-10	0.750	1.000	(25.400)	M71-R6200	\$251.62
Fig. 6	M71-18-498	250	B-498	White	12-10	0.750	1.000	(25.400)	M71-R6200	\$37.03
Fig. 12	M71-17-498	500	B-498	White	12-10	1.000	0.500	(12.700)	M71-R6200	\$56.62
Fig. 12	M71-19-499	250	B-499	White	12-10	1.000	1.000	(25.400)	M71-R4300	\$41.09
Fig. 12	BM71-19-498*	2500	B-498	White	12-10	1.000	1.000	(25.400)	M71-R6200	\$272.93
Fig. 12	M71-19-498	250	B-498	White	12-10	1.000	1.000	(25.400)	M71-R6200	\$40.18
Fig. 4	M71-78-499	250	B-499	White	12-10	1.900	1.000	(25.400)	M71-R4300	\$65.81
Fig. 6	M71-28-499	750	B-499	White	10-4	0.250	1.500	(38.100)	M71-R4300	\$53.52
Fig. 6	M71-29-499	500	B-499	White	10-4	0.500	1.500	(38.100)	M71-R4300	\$51.02
Fig. 6	BM71-29-498*	5000	B-498	White	10-4	0.500	1.500	(38.100)	M71-R6200	\$339.55
Fig. 6	M71-29-498	500	B-498	White	10-4	0.500	1.500	(38.100)	M71-R6200	\$49.98
Fig. 6	M71-30-499	250	B-499	White	10-4	0.750	1.500	(38.100)	M71-R4300	\$45.16
Fig. 6	M71-30-498	250	B-498	White	10-4	0.750	1.500	(38.100)	M71-R6200	\$43.97
Fig. 6	M71-31-499	250	B-499	White	10-4	1.000	1.500	(38.100)	M71-R4300	\$52.34
Fig. 6	M71-31-498	250	B-498	White	10-4	1.000	1.500	(38.100)	M71-R6200	\$51.02
Fig. 12	M71-32-498	250	B-498	White	10-4	1.500	1.500	(38.100)	M71-R6200	\$63.19
Fig. 5	M71C-240-498	1 Roll (cont.)	B-498	White	-	0.240	30 ft.	(9.10 m)	M71-R6200	\$42.39
Fig. 8	BM71C-240-498*	1 Roll (cont.)	B-498	White	-	0.240	275 ft.	(83.82 m)	M71-R6200	\$272.50
Fig. 5	M71C-318-498	1 Roll (cont.)	B-498	White	-	0.318	30 ft.	(9.10 m)	M71-R6200	\$43.56
Fig. 5	BM71C-318-498*	1 Roll (cont.)	B-498	White	-	0.318	275 ft.	(83.82 m)	M71-R6200	\$279.48
Fig. 5	M71C-375-498	1 Roll (cont.)	B-498	White	-	0.375	30 ft.	(9.10 m)	M71-R6200	\$44.24
Fig. 5	BM71C-375-498*	1 Roll (cont.)	B-498	White	-	0.375	275 ft.	(83.82 m)	M71-R6200	\$283.89
Fig. 8	M71C-500-499	1 Roll (cont.)	B-499	White	-	0.500	30 ft.	(9.10 m)	M71-R4300	\$31.72
Fig. 8	M71C-500-498	1 Roll (cont.)	B-498	White	-	0.500	30 ft.	(9.10 m)	M71-R6200	\$31.72
Fig. 4	M71-84-499	500	B-499	White	-	0.900	0.500	(12.700)	M71-R4300	\$47.24
Fig. 4	M71-17-489	500	B-489	White	-	1.000	0.500	(12.700)	M71-R4300	\$56.52
Fig. 8	M71C-1000-499	1 Roll (cont.)	B-499	White	-	1.000	30 ft.	(9.10 m)	M71-R4300	\$44.25
Fig. 8	M71C-1000-498	1 Roll (cont.)	B-498	White	-	1.000	30 ft.	(9.10 m)	M71-R6200	\$44.25
Fig. 4	M71-81-499	750	B-499	White	-	1.900	0.250	(6.350)	M71-R4300	\$62.68
Fig. 8	M71C-1900-499	1 Roll (cont.)	B-499	White	-	1.900	30 ft.	(9.10 m)	M71-R4300	\$66.40
Fig. 8	M71C-1900-498	1 Roll (cont.)	B-498	White	-	1.900	30 ft.	(9.10 m)	M71-R6200	\$66.40

Fiber Optic Flags

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)		Recommended Ribbon	Price	
						B Inch				
Fig. 23	M71FP-1-425	250	B-425	White	1.180	0.788	(30.000)	(20.000)	M71-R4300	\$24.20
Fig. 24	M71FT-1-425	250	B-425	White	1.180	0.788	(30.000)	(20.000)	M71-R4300	\$24.20
Fig. 23	M71FP-2-425	100	B-425	White	1.750	1.000	(44.450)	(25.400)	M71-R4300	\$24.20



* "B" indicates bulk roll.

See all ribbon colors on page 115.

BMP[®]71 Label Printer Materials

www.BradyID.com/bmp71

Sign And Label Printers

Self Laminating Wire Markers

Protected printing area offers superior chemical and abrasion resistance. Features a non-printed clear area that wraps around and overlaminates the printed text.




Figure 4




Figure 7




Figure 19



Self-Laminating Labels

Diagram	Part Number	Labels/Roll	Material	Color	Approx. Wire Gauge	A Inch	(mm)	Label Dimensions B Inch	(mm)	C Inch	(mm)	Recommended Ribbon	Price
Fig. 7	BM71-21-427*	1000	B-427	White	Cables	1.000	(25.400)	2.500	(63.500)	0.750	(19.050)	M71-R4300	\$191.55
Fig. 7	M71-21-427	100	B-427	White	Cables	1.000	(25.400)	2.500	(63.500)	0.750	(19.050)	M71-R4300	\$27.36
Fig. 7	M71-21-427-YL	100	B-427	Yellow	Cables	1.000	(25.400)	2.500	(63.500)	0.750	(19.050)	M71-R4300	\$34.28
Fig. 19	BM71-64-427*	1000	B-427	White	Cables	1.000	(25.400)	3.375	(85.730)	1.125	(28.580)	M71-R4300	\$117.29
Fig. 19	M71-64-427	100	B-427	White	Cables	1.000	(25.400)	3.375	(85.730)	1.125	(28.580)	M71-R4300	\$16.75
Fig. 7	BM71-23-427*	1000	B-427	White	Cables	1.000	(25.400)	4.000	(101.600)	1.000	(25.400)	M71-R4300	\$228.72
Fig. 7	M71-23-427	100	B-427	White	Cables	1.000	(25.400)	4.000	(101.600)	1.000	(25.400)	M71-R4300	\$32.58
Fig. 7	BM71-109-427*	500	B-427	White	Cables	1.500	(38.100)	4.000	(101.600)	1.500	(38.100)	M71-R4300	\$154.25
Fig. 7	BM71-33-427*	500	B-427	White	Cables	1.500	(38.100)	4.000	(101.600)	1.000	(25.400)	M71-R4300	\$154.25
Fig. 7	M71-109-427	100	B-427	White	Cables	1.500	(38.100)	4.000	(101.600)	1.500	(38.100)	M71-R4300	\$44.09
Fig. 7	M71-33-427	100	B-427	White	Cables	1.500	(38.100)	4.000	(101.600)	1.000	(25.400)	M71-R4300	\$44.09
Fig. 7	M71-33-427-YL	100	B-427	Yellow	Cables	1.500	(38.100)	4.000	(101.600)	1.000	(25.400)	M71-R4300	\$55.22
Fig. 7	BM71-34-427*	500	B-427	White	Cables	1.500	(38.100)	6.000	(152.400)	1.500	(38.100)	M71-R4300	\$255.41
Fig. 7	M71-34-427	50	B-427	White	Cables	1.500	(38.100)	6.000	(152.400)	1.500	(38.100)	M71-R4300	\$36.51
Fig. 7	M71-66-427	100	B-427	White	Cables	1.938	(49.230)	3.150	(80.000)	1.000	(25.400)	M71-R4300	\$44.09
Fig. 7	M71-10-427	750	B-427	White	16-10	0.250	(6.350)	0.750	(19.050)	0.375	(9.530)	M71-R4300	\$34.94
Fig. 7	BM71-11-427*	5000	B-427	White	16-10	0.500	(12.700)	0.750	(19.050)	0.375	(9.530)	M71-R4300	\$260.12
Fig. 7	M71-11-427	500	B-427	White	16-10	0.500	(12.700)	0.750	(19.050)	0.375	(9.530)	M71-R4300	\$37.15
Fig. 7	M71-96-427	250	B-427	White	16-10	1.000	(25.400)	0.750	(19.050)	0.375	(9.530)	M71-R4300	\$25.37
Fig. 7	BM71-17-427*	5000	B-427	White	12-10	0.500	(12.700)	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$278.19
Fig. 7	M71-17-427	500	B-427	White	12-10	0.500	(12.700)	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$39.78
Fig. 7	BM71-19-427*	2500	B-427	White	12-10	1.000	(25.400)	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$29.67
Fig. 7	M71-19-427	250	B-427	White	12-10	1.000	(25.400)	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$35.73
Fig. 7	M71-19-427-YL	250	B-427	Yellow	12-10	1.000	(25.400)	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$39.38
Fig. 7	M71-104-427	250	B-427	White	12-10	1.500	(38.100)	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$45.08
Fig. 7	M71-28-427	750	B-427	White	10-4	0.250	(6.350)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$44.49
Fig. 7	BM71-29-427*	5000	B-427	White	10-4	0.500	(12.700)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$340.19
Fig. 7	M71-29-427	500	B-427	White	10-4	0.500	(12.700)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$48.67
Fig. 7	BM71-18-427*	2500	B-427	White	10-4	0.750	(19.050)	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$227.81
Fig. 7	M71-18-427	250	B-427	White	10-4	0.750	(19.050)	1.000	(25.400)	0.375	(9.530)	M71-R4300	\$32.47
Fig. 7	BM71-30-427*	2500	B-427	White	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$253.45
Fig. 7	M71-30-427	250	B-427	White	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$36.25
Fig. 7	M71-30-427-BL	250	B-427	Blue	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$45.28
Fig. 7	M71-30-427-PL	250	B-427	Purple	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$45.28
Fig. 7	M71-30-427-RD	250	B-427	Red	10-4	0.750	(19.050)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$45.28
Fig. 7	M71-103-427	250	B-427	White	10-4	1.000	(25.400)	1.250	(31.750)	0.500	(12.700)	M71-R4300	\$42.14
Fig. 7	BM71-31-427*	2500	B-427	White	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$321.24
Fig. 7	M71-31-427	250	B-427	White	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$45.80
Fig. 7	M71-31-427-GN	250	B-427	Green	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$58.37
Fig. 7	M71-31-427-RD	250	B-427	Red	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$58.37
Fig. 7	M71-31-427-YL	250	B-427	Yellow	10-4	1.000	(25.400)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$58.37
Fig. 4	M71-30-427-AW	250	B-427	White	10-4	1.500	(38.100)	0.750	(19.050)	-	-	M71-R4300	\$36.25
Fig. 7	BM71-32-427*	1000	B-427	White	10-4	1.500	(38.100)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$135.15
Fig. 7	M71-32-427	250	B-427	White	10-4	1.500	(38.100)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$47.36
Fig. 7	M71-32-427-YL	250	B-427	Yellow	10-4	1.500	(38.100)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$58.75
Fig. 7	M71-88-427	250	B-427	White	10-4	1.750	(44.450)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$61.89
Fig. 7	BM71-107-427*	1000	B-427	White	10-4	2.000	(50.800)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$384.69
Fig. 7	M71-107-427	100	B-427	White	10-4	2.000	(50.800)	1.500	(38.100)	0.500	(12.700)	M71-R4300	\$56.57

* "B" indicates bulk roll.

See all ribbon colors on page 115.

PermaSleeves Wire Markers

These full circle heat-shrink sleeves are the ultimate in marker durability, permanence and aesthetic appearance. Fast shrink rate saves time and costs during installation.




Figure 8





Figure 20



PermaSleeve Markers (Shrink Ratio 3-to-1)

Diagram	Part Number	Labels/Roll	Material	Color	Approx. Wire Gauge	A Inch	Label Dimensions (mm)	B Inch	(mm)	Recommended Ribbon	Price
Fig. 20	M71-94-1-342	100	B-342	White	28-18	1.015	(25.780)	0.182	(4.620)	M71-R4300	\$45.67
Fig. 20	M71-94-1-342YL	100	B-342	Yellow	28-18	1.015	(25.780)	0.182	(4.620)	M71-R4300	\$46.05
Fig. 20	BM71-94-175-342*	2500	B-342	White	28-18	1.765	(44.830)	0.182	(4.620)	M71-R4300	\$1,083.78
Fig. 20	BM71-94-175-342YL*	2500	B-342	Yellow	28-18	1.765	(44.830)	0.182	(4.620)	M71-R4300	\$1,083.78
Fig. 20	M71-94-175-342	100	B-342	White	28-18	1.765	(44.830)	0.182	(4.620)	M71-R4300	\$62.02
Fig. 20	M71-94-175-342YL	100	B-342	Yellow	28-18	1.765	(44.830)	0.182	(4.620)	M71-R4300	\$62.02
Fig. 8	BM71C-125-342*	1 Roll (cont.)	B-342	White	22-16	0.235	(5.960)	50 ft.	(15.24 m)	M71-R4300	\$212.06
Fig. 20	BM71-125-1-342*	1000	B-342	White	22-16	1.015	(25.780)	0.235	(5.960)	M71-R4300	\$338.23
Fig. 20	M71-125-1-342	100	B-342	White	22-16	1.015	(25.780)	0.235	(5.960)	M71-R4300	\$48.41
Fig. 20	M71-125-1-342YL	100	B-342	Yellow	22-16	1.015	(25.780)	0.235	(5.960)	M71-R4300	\$48.41
Fig. 20	BM71-125-175-342*	1000	B-342	White	22-16	1.765	(44.830)	0.235	(5.960)	M71-R4300	\$454.43
Fig. 20	BM71-125-175-342YL*	1000	B-342	Yellow	22-16	1.765	(44.830)	0.235	(5.960)	M71-R4300	\$454.43
Fig. 20	M71-125-175-342	100	B-342	White	22-16	1.765	(44.830)	0.235	(5.960)	M71-R4300	\$65.03
Fig. 20	M71-125-175-342YL	100	B-342	Yellow	22-16	1.765	(44.830)	0.235	(5.960)	M71-R4300	\$65.03
Fig. 8	BM71C-187-342*	1 Roll (cont.)	B-342	White	18-12	0.335	(8.500)	50 ft.	(15.24 m)	M71-R4300	\$224.91
Fig. 20	BM71-187-1-342*	100	B-342	White	18-12	1.015	(25.780)	0.335	(8.500)	M71-R4300	\$377.35
Fig. 20	BM71-187-1-342YL*	1000	B-342	Yellow	18-12	1.015	(25.780)	0.335	(8.500)	M71-R4300	\$377.35
Fig. 20	M71-187-1-342	100	B-342	White	18-12	1.015	(25.780)	0.335	(8.500)	M71-R4300	\$53.91
Fig. 20	M71-187-1-342YL	100	B-342	Yellow	18-12	1.015	(25.780)	0.335	(8.500)	M71-R4300	\$53.91
Fig. 20	BM71-187-175-342*	1000	B-342	White	18-12	1.765	(44.830)	0.335	(8.500)	M71-R4300	\$491.19
Fig. 20	BM71-187-175-342YL*	1000	B-342	Yellow	18-12	1.765	(44.830)	0.335	(8.500)	M71-R4300	\$491.19
Fig. 20	M71-187-175-342	100	B-342	White	18-12	1.765	(44.830)	0.335	(8.500)	M71-R4300	\$72.22
Fig. 20	M71-187-175-342YL	100	B-342	Yellow	18-12	1.765	(44.830)	0.335	(8.500)	M71-R4300	\$72.22
Fig. 8	BM71C-250-342*	1 Roll (cont.)	B-342	White	16-10	0.439	(11.150)	50 ft.	(15.24 m)	M71-R4300	\$289.17
Fig. 20	BM71-250-1-342*	1000	B-342	White	16-10	1.015	(25.780)	0.439	(11.150)	M71-R4300	\$456.52
Fig. 20	M71-250-1-342	100	B-342	White	16-10	1.015	(25.780)	0.439	(11.150)	M71-R4300	\$65.30
Fig. 20	M71-250-1-342YL	100	B-342	Yellow	16-10	1.015	(25.780)	0.439	(11.150)	M71-R4300	\$65.30
Fig. 20	BM71-250-175-342*	1000	B-342	White	16-10	1.765	(44.830)	0.439	(11.150)	M71-R4300	\$614.58
Fig. 20	BM71-250-175-342YL*	1000	B-342	Yellow	16-10	1.765	(44.830)	0.439	(11.150)	M71-R4300	\$614.58
Fig. 20	M71-250-175-342	100	B-342	White	16-10	1.765	(44.830)	0.439	(11.150)	M71-R4300	\$87.93
Fig. 20	M71-250-175-342YL	100	B-342	Yellow	16-10	1.765	(44.830)	0.439	(11.150)	M71-R4300	\$87.65
Fig. 8	BM71C-375-342*	1 Roll (cont.)	B-342	White	12-6	0.645	(16.380)	50 ft.	(15.24 m)	M71-R4300	\$424.12
Fig. 20	BM71-375-1-342*	1000	B-342	White	12-6	1.015	(25.780)	0.645	(16.380)	M71-R4300	\$673.71
Fig. 20	M71-375-1-342	100	B-342	White	12-6	1.015	(25.780)	0.645	(16.380)	M71-R4300	\$96.19
Fig. 20	M71-375-1-342YL	100	B-342	Yellow	12-6	1.015	(25.780)	0.645	(16.380)	M71-R4300	\$96.19
Fig. 20	BM71-375-175-342*	1000	B-342	White	12-6	1.765	(44.830)	0.645	(16.380)	M71-R4300	\$905.32
Fig. 20	M71-375-175-342	100	B-342	White	12-6	1.765	(44.830)	0.645	(16.380)	M71-R4300	\$129.40
Fig. 20	M71-375-175-342YL	100	B-342	Yellow	12-6	1.765	(44.830)	0.645	(16.380)	M71-R4300	\$129.40
Fig. 8	BM71C-500-342*	1 Roll (cont.)	B-342	White	8-1	0.851	(21.610)	50 ft.	(15.24 m)	M71-R4300	\$488.38
Fig. 20	BM71-500-1-342*	1000	B-342	White	8-1	1.015	(25.780)	0.851	(21.610)	M71-R4300	\$778.39
Fig. 20	BM71-500-1-342YL*	1000	B-342	Yellow	8-1	1.015	(25.780)	0.851	(21.610)	M71-R4300	\$778.39
Fig. 20	M71-500-1-342	100	B-342	White	8-1	1.015	(25.780)	0.851	(21.610)	M71-R4300	\$111.12
Fig. 20	M71-500-1-342YL	100	B-342	Yellow	8-1	1.015	(25.780)	0.851	(21.610)	M71-R4300	\$111.12
Fig. 20	BM71-500-175-342*	1000	B-342	White	8-1	1.765	(44.830)	0.851	(21.610)	M71-R4300	\$1,047.15
Fig. 20	BM71-500-175-342YL*	1000	B-342	Yellow	8-1	1.765	(44.830)	0.851	(21.610)	M71-R4300	\$1,047.15
Fig. 20	M71-500-175-342	100	B-342	White	8-1	1.765	(44.830)	0.851	(21.610)	M71-R4300	\$149.54
Fig. 20	M71-500-175-342YL	100	B-342	Yellow	8-1	1.765	(44.830)	0.851	(21.610)	M71-R4300	\$149.54
Fig. 20	M71-1000-1-342	50	B-342	White	1-500	1.015	(25.780)	1.660	(42.160)	M71-R4300	\$76.82
Fig. 20	M71-1000-1-342YL	50	B-342	Yellow	1-500	1.015	(25.780)	1.660	(42.160)	M71-R4300	\$76.82
Fig. 8	BM71C-1000-342*	1 Roll (cont.)	B-342	White	1-500	1.660	(42.160)	50 ft.	(15.24 m)	M71-R4300	\$674.73
Fig. 20	BM71-1000-175-342*	500	B-342	White	1-500	1.765	(44.830)	1.660	(42.160)	M71-R4300	\$728.01
Fig. 20	M71-1000-175-342	50	B-342	White	1-500	1.765	(44.830)	1.660	(42.160)	M71-R4300	\$104.04
Fig. 20	M71-1000-175-342YL	50	B-342	Yellow	1-500	1.765	(44.830)	1.660	(42.160)	M71-R4300	\$104.04

Tags

Diagram	Part Number	Labels/Roll	Material	Color	A Inch (mm)	Label Dimensions B Inch (mm)	Recommended Ribbon	Price
Fig. 26	M71-111-145FR-GY	100	B-145FR	Grey	1.206 (30.630)	0.758 (19.250)	M71-R6000	\$35.99
Fig. 26	BM71-111-145-GY*	1000	B-145	Grey	1.206 (30.630)	0.758 (19.250)	M71-R6000	\$228.99
Fig. 26	M71-111-145-GY	100	B-145	Grey	1.206 (30.630)	0.758 (19.250)	M71-R6000	\$32.70
Fig. 26	M71-110-145FR-GY	100	B-145FR	Grey	1.750 (44.450)	1.000 (25.400)	M71-R6000	\$35.99
Fig. 26	BM71-110-145-GY*	1000	B-145	Grey	1.750 (44.450)	1.000 (25.400)	M71-R6000	\$228.99
Fig. 26	M71-110-145-GY	100	B-145	Grey	1.750 (44.450)	1.000 (25.400)	M71-R6000	\$32.70




Figure 26

* "B" indicates bulk roll.


See all ribbon colors on page 115.

BMP[®]71 Label Printer Materials

www.BradyID.com/bmp71

Voice/Data Comm

Durable materials with permanent adhesive in a variety of sizes for marking racks, bays, frames, slots, and other voice/data equipment.



Die Cut Labels

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)		B Inch (mm)	Recommended Ribbon	Price
Fig. 4	M71-45-422	500	B-422	White	1.500	(38.100)	0.375 (9.530)	M71-R6000	\$52.73	
Fig. 4	M71-30-422	250	B-422	White	1.500	(38.100)	0.750 (19.050)	M71-R6000	\$49.41	
Fig. 4	BM71-20-422*	1000	B-422	White	2.000	(50.800)	1.000 (25.400)	M71-R6000	\$193.42	
Fig. 4	M71-37-422	100	B-422	White	3.000	(76.200)	1.900 (48.260)	M71-R6000	\$41.23	

Specialty Continuous Tape


Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)		B Inch (mm)	Recommended Ribbon	Price
Fig. 8	M71C-375-422	1 Roll (cont.)	B-422	White	0.375	(9.530)	50 ft. (15.24 m)	M71-R6000	\$58.80	
Fig. 5	M71C-475-422	1 Roll (cont.)	B-422	White	0.475	(12.100)	50 ft. (15.24 m)	M71-R6000	\$67.63	
Fig. 8	M71C-500-422	1 Roll (cont.)	B-422	White	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$58.80	
Fig. 8	M71C-625-422	1 Roll (cont.)	B-422	White	0.625	(15.880)	50 ft. (15.24 m)	M71-R6000	\$81.92	
Fig. 8	M71C-1000-422	1 Roll (cont.)	B-422	White	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$81.28	
Fig. 8	M71C-1900-422	1 Roll (cont.)	B-422	White	1.900	(48.260)	50 ft. (15.24 m)	M71-R6000	\$121.83	

Tags

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)		B Inch (mm)	Recommended Ribbon	Price
Fig. 3	M71C-230-412	1 Roll (cont.)	B-412	White	0.230	(5.840)	50 ft. (15.24 m)	M71-R6200	\$48.54	
Fig. 3	M71C-375-412	1 Roll (cont.)	B-412	White	0.375	(9.530)	50 ft. (15.24 m)	M71-R6200	\$51.16	
Fig. 5	M71C-475-412	1 Roll (cont.)	B-412	White	0.475	(12.100)	50 ft. (15.24 m)	M71-R6200	\$53.91	
Fig. 3	M71C-500-412	1 Roll (cont.)	B-412	White	0.500	(12.700)	50 ft. (15.24 m)	M71-R6200	\$53.91	
Fig. 5	M71C-625-412	1 Roll (cont.)	B-412	White	0.625	(15.900)	50 ft. (15.24 m)	M71-R6200	\$65.29	
Fig. 3	M71C-785-412	1 Roll (cont.)	B-412	White	0.785	(19.940)	50 ft. (15.24 m)	M71-R6200	\$74.58	
Fig. 31	BM71-40-412*	5000	B-412	White	1.938	(49.230)	0.375 (9.530)	M71-R6200	\$284.59	
Fig. 31	M71-40-412	750	B-412	White	1.938	(49.230)	0.375 (9.530)	M71-R6200	\$61.11	

Printable Tags

Polyethylene material that is tear and chemical/solvent resistance.



Tags

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)		B Inch (mm)	Recommended Ribbon	Price
Fig. 21	M71-36-109	250	B-109	White	1.125	(28.570)	1.750 (44.450)	M71-R4300	\$49.20	
Fig. 32	BM71-12-109*	1000	B-109	White	3.000	(76.200)	0.750 (19.050)	M71-R4300	\$257.24	
Fig. 32	M71-12-109	100	B-109	White	3.000	(76.200)	0.750 (19.050)	M71-R4300	\$36.77	

* "B" indicates bulk roll.
See all ribbon colors on page 115.

Tamper Indicating

Tamper resistant tape destructs into tiny fragments when being removed. Making any attempts to remove the label very difficult and time consuming.




Figure 4



Figure 8



Tamper Resistant Labels

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch (mm)	Recommended Ribbon	Price
Fig. 4	M71-17-352	500	B-352	Silver	1.000	(25.400)	0.500 (12.700)	M71-R6000	\$54.17
Fig. 4	M71-17-351	500	B-351	White	1.000	(25.400)	0.500 (12.700)	M71-R6200	\$53.79
Fig. 4	M71-31-352	250	B-352	Silver	1.500	(38.100)	1.000 (25.400)	M71-R6000	\$43.21
Fig. 4	M71-31-351	250	B-351	White	1.500	(38.100)	1.000 (25.400)	M71-R6200	\$47.82
Fig. 4	M71-20-352	100	B-352	Silver	2.000	(50.800)	1.000 (25.400)	M71-R6000	\$33.02
Fig. 4	M71-20-351	100	B-351	White	2.000	(50.800)	1.000 (25.400)	M71-R6200	\$33.02
Fig. 4	M71-37-352	100	B-352	Silver	3.000	(76.200)	1.900 (48.260)	M71-R6000	\$47.70
Fig. 4	M71-37-351	100	B-351	White	3.000	(76.200)	1.900 (48.260)	M71-R6200	\$47.82

Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch (mm)	Recommended Ribbon	Price
Fig. 8	M71C-500-530	1 Roll (cont.)	B-530	White	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$57.27
Fig. 8	M71C-1000-530	1 Roll (cont.)	B-530	White	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$75.91
Fig. 8	M71C-2000-530	1 Roll (cont.)	B-530	White	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$113.19

Static Dissipative

Low profile polyimide material that has a static dissipative liner. Primarily used for printed circuit boards and electronic component labeling.




Figure 4



Die Cut Labels

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch (mm)	Recommended Ribbon	Price
Fig. 4	M71-4-478	500	B-478	White	0.400	(10.160)	0.400 (10.160)	M71-R6000	\$76.06
Fig. 4	M71-9-478	750	B-478	White	0.650	(16.510)	0.200 (5.080)	M71-R6000	\$116.44
Fig. 4	M71-14-477	750	B-477	White	1.000	(25.400)	0.187 (4.750)	M71-R6000	\$147.14
Fig. 4	M71-25-478	750	B-478	White	1.250	(31.750)	0.250 (6.350)	M71-R6000	\$146.81
Fig. 4	M71-2-477	100	B-477	White	2.000	(50.800)	0.250 (6.350)	M71-R6000	\$41.70

Laboratory Identification

Self Laminating labels are great for vials, tubes, straws and more. Good for high and low temperature applications.



Figure 1




Figure 15




Figure 18



Self Laminating Labels

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch (mm)	C Inch (mm)	Recommended Ribbon	Price
Fig. 1	M71-82-499	500	B-499	White	0.375 dia.	(9.53 dia.)	-	-	M71-R4300	\$33.76
Fig. 1	M71-83-499	500	B-499	White	0.500 dia.	(12.70 dia.)	-	-	M71-R4300	\$33.76
Fig. 15	M71-98-499	500	B-499	White	1.000	(25.400)	0.375 (9.530)	0.37 dia (9.53 dia.)	M71-R4300	\$66.61
Fig. 18	BM71-75-461*	1000	B-461	White	1.000	(25.400)	2.625 (66.680)	1.000 (25.400)	M71-R4300	\$245.67

* "B" indicates bulk roll.

See all ribbon colors on page 115.

BMP®71 Label Printer Materials

www.BradyID.com/bmp71

Temporary/Removable

These indoor labels are designed with special adhesive that makes it easy to remove and re-apply.



Figure 8



Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch (mm)	Recommended Ribbon	Price
Fig. 8	M71C-500-581-WT	1 Roll (cont.)	B-581	White	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$50.36
Fig. 8	M71C-500-581-YL	1 Roll (cont.)	B-581	Yellow	0.500	(12.700)	50 ft. (15.24 m)	M71-R6000	\$50.36
Fig. 8	M71C-1000-581-WT	1 Roll (cont.)	B-581	White	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$70.52
Fig. 8	M71C-1000-581-YL	1 Roll (cont.)	B-581	Yellow	1.000	(25.400)	50 ft. (15.24 m)	M71-R6000	\$70.52
Fig. 8	M71C-2000-581-WT	1 Roll (cont.)	B-581	White	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$106.53
Fig. 8	M71C-2000-581-YL	1 Roll (cont.)	B-581	Yellow	2.000	(50.800)	50 ft. (15.24 m)	M71-R6000	\$106.53

Reflective/Glow In The Dark Applications

B-582 Bradyglo phosphorescent material is light absorbing and will glow for 10 hours. B-584 reflective material helps to illuminate the labels when light is shined on the surface.

These two materials are great for egress and other critical pieces of information.




Figure 8



Specialty Continuous Tape

Diagram	Part Number	Labels/Roll	Material	Color	A Inch	Label Dimensions (mm)	B Inch (mm)	Recommended Ribbon	Price
Fig. 8	BM71C-1000-584-OR*	1 Roll (cont.)	B-584	Reflective Orange	1.000	(25.400)	75 ft. (22.86 m)	M71-R6000	\$131.94
Fig. 8	BM71C-1000-584-WT*	1 Roll (cont.)	B-584	Reflective Silver	1.000	(25.400)	75 ft. (22.86 m)	M71-R6000	\$131.94
Fig. 8	BM71C-1000-584-YL*	1 Roll (cont.)	B-584	Reflective Yellow	1.000	(25.400)	75 ft. (22.86 m)	M71-R6000	\$131.94
Fig. 8	BM71C-1000-582*	1 Roll (cont.)	B-582	Phosphorescent	1.000	(25.400)	75 ft. (22.86 m)	M71-R6000	\$131.94
Fig. 8	BM71C-2000-584-OR*	1 Roll (cont.)	B-584	Reflective Orange	2.000	(50.800)	75 ft. (22.86 m)	M71-R6000	\$211.35
Fig. 8	BM71C-2000-584-WT*	1 Roll (cont.)	B-584	Reflective White	2.000	(50.800)	75 ft. (22.86 m)	M71-R6000	\$211.35
Fig. 8	BM71C-2000-584-YL*	1 Roll (cont.)	B-584	Reflective Yellow	2.000	(50.800)	75 ft. (22.86 m)	M71-R6000	\$211.35
Fig. 8	BM71C-2000-582*	1 Roll (cont.)	B-582	Phosphorescent	2.000	(50.800)	75 ft. (22.86 m)	M71-R6000	\$211.35

* "B" indicates bulk roll.

See all ribbon colors on page 115.



ToughStripe® Print-On-Demand Floor Labels

- Create custom-printed floor labels using your BMP®71 Label Printer!
- Same durability and performance as ToughStripe® floor marking tape
- Easy 3-step process: print label, position on floor, apply overlaminate

Description	Catalog Number	
	1" x 50'	2" x 50'
White	M71-1000-483-WT-KT	M71-2000-483-WT-KT
Black	M71-1000-483-BK-KT	M71-2000-483-BK-KT
Yellow	M71-1000-483-YL-KT	M71-2000-483-YL-KT
Red	M71-1000-483-RD-KT	M71-2000-483-RD-KT
Blue	M71-1000-483-BL-KT	M71-2000-483-BL-KT
Green	M71-1000-483-GN-KT	M71-2000-483-GN-KT
Orange	M71-1000-483-OR-KT	M71-2000-483-OR-KT





Figure 8



BMP®71 Label Printer Materials

www.BradyID.com/bmp71



BMP®71 Ribbons

Part Number	Description	Size	Price
M71-R4300	Black Ribbon	150' (45.72 m)	\$56.34
M71-R6000	Black Ribbon	150' (45.72 m)	\$56.34
M71-R6200	Black Ribbon	150' (45.72 m)	\$56.34
M71-R6400	Black Ribbon	150' (45.72 m)	\$61.97
M71-R6600	Black Ribbon	150' (45.72 m)	\$73.34
M71-R4400-WT	White Ribbon	150' (45.72 m)	\$66.59

Part Number	Description	Size	Price
M71-R6800-WT	White Ribbon	150' (45.72 m)	\$73.34
M71-R6900-RD	Red Ribbon	150' (45.72 m)	\$66.59
M71-R6900-BL	Blue Ribbon	150' (45.72 m)	\$66.59
M71-R6900-GR	Green Ribbon	150' (45.72 m)	\$66.59
M71-R6900-MA	Magenta Ribbon	150' (45.72 m)	\$66.59
M71-R6900-YL	Yellow Ribbon	150' (45.72 m)	\$66.59

B-Number	Material	M71-R4300 (Black)	M71-R6000 (Black)	M71-R6200 (Black)	M71-R6400 (Black)	M71-R6600 (Black)	M71-R4400-WT (White)	M71-R6800-WT (White)	M71-R6900 (Colors)
B-109	Tag	●	-	▲	-	-	-	-	-
B-145	Tag	-	●	-	-	-	▲	-	-
B-145FR	Tag	-	●	-	-	-	▲	-	▲
B-321*	Polyolefin	-	-	●	-	-	-	-	-
B-341	Polyolefin	●	-	-	-	-	-	-	-
B-342	Polyolefin	●	-	-	-	-	-	-	-
B-345*	High Temp Sleeve	-	-	-	-	●	-	▲	-
B-351	Vinyl	-	-	●	-	-	-	-	-
B-352	Vinyl	-	●	-	-	-	▲	-	▲
B-353*	Paper	●	-	-	-	-	-	-	-
B-390*	Polypropylene	-	●	-	-	-	▲	-	▲
B-412	Polypropylene	▲	-	●	-	-	-	-	-
B-422	Polyester	-	● UL	-	-	-	▲	-	▲
B-423	Polyester	-	● UL	▲	-	-	▲	-	▲
B-424	Paper	●	-	-	-	-	-	-	-
B-425	Polyimide	●	-	-	-	-	-	-	-
B-426	Polyimide	●	-	-	-	-	-	-	-
B-427	Vinyl	● UL	-	▲	-	-	-	-	-
B-428	Polyester	● UL	-	-	-	-	-	-	-
B-430	Polyester	-	● UL	▲	-	-	▲	-	▲
B-432*	Polyester	-	● UL	-	-	-	▲	-	▲
B-433*	Polyester	-	● UL	-	-	-	▲	-	▲
B-435*	Polyester	-	● UL	-	-	-	▲	-	▲
B-439*	Vinyl	-	●	▲	-	-	▲	-	▲
B-457	Polyimide	-	● UL	-	-	-	▲	-	▲
B-459	Polyester	-	● UL	-	-	-	▲	-	▲
B-461	Polyester	●	-	▲	-	-	-	-	-
B-473	Polyester	-	● UL	▲	-	-	▲	-	▲
B-477	Polyimide	-	● UL	▲	-	-	▲	-	▲
B-478	Polyimide	-	● UL	-	-	-	▲	-	▲
B-479*	Polyimide	-	● UL	-	-	-	▲	-	▲
B-481*	Polyester	-	-	-	●	-	-	-	-
B-483	Polyester	-	● UL	▲	-	-	▲	-	▲
B-486	Polyester	● UL	-	-	-	-	-	-	-
B-488	Polyester	● UL	-	▲	-	-	-	-	-
B-489	Polyester	● UL	-	-	-	-	-	-	-
B-490*	Polyester	●	-	-	-	-	-	-	-
B-495*	Polyethylene Napthalate	-	● UL	-	-	-	▲	-	▲
B-498	Vinyl Cloth	▲	-	●	-	-	-	-	-
B-499	Nylon Cloth	● UL	-	▲	-	-	-	-	-
B-529	Polypropylene	-	●	-	-	-	▲	-	▲
B-530	Tamper Resistant	-	●	-	-	-	▲	-	▲
B-580	Vinyl	-	●	-	-	-	▲	-	▲
B-581	Vinyl	-	●	-	-	-	▲	-	▲
B-582	Phosphorescent	-	●	-	-	-	▲	-	▲
B-584	Reflective	-	●	-	-	-	▲	-	▲
B-593	Polyester	-	●	-	-	-	▲	-	▲
B-7531*	Metalized Polyester	●	-	-	-	-	-	-	-
B-7536*	Polyester	-	-	●	-	-	-	-	-
B-7546*	Tamper-Evident Polyester	-	● UL	-	-	-	▲	-	▲
B-7551*	Polyester	-	-	●	-	-	-	-	-
B-7566*	Tamper-Evident Polyester	-	●	-	-	-	▲	-	▲
B-7576*	Tamper-Evident Metalized Polyester	-	● UL	-	-	-	-	-	-
B-7593*	Polyethelene	-	●	-	-	-	▲	-	▲
B-7596*	Vinyl	-	-	●	-	-	-	-	-
B-7597*	Polyethelene	●	-	-	-	-	-	-	-
B-7599*	Polyethelene Tag	●	-	-	-	-	-	-	-
B-7643*	Thermosplastic Polyether Polyurethane	-	●	-	-	-	▲	-	▲
B-7696*	Vinyl Tag	-	●	-	-	-	▲	-	▲
B-8425*	Polypropylene	-	● UL	-	-	-	▲	-	▲

●	Recommended ribbon for use with respective material.
▲	Acceptable ribbon for use with respective material.
UL	These materials are UL recognized with its respective ribbon.

*TLS®2200 materials that can be used in the BMP®71 Label Printer.
 Tedlar® is a registered trademark of DuPont.

BMP[®]21 Label Printer

www.BradyID.com/bmp21

Sign And Label Printers

BMP[®]21 LABEL PRINTER

An affordable label and wire marker designed for the tool box



Electrical Labeling



Datacomm Labeling



General Identification



PermaSleeve Markers



Self-Laminating Labels



Safety Labels

...and many more.



MEET THE NEWEST MEMBER OF YOUR CREW

- One-handed operation with large display and backlight
- Terminal block and patch panel options
- Advanced serialization, barcoding and symbols
- Cuts and holds printed labels until you need them
- Rugged construction...withstands a 5 ft. drop onto concrete

BMP[®]21 Label Printer & Accessories

Catalog #	Description	Price Each
BMP21	BMP21 Label Printer	\$145.95
BMP21-HC	BMP21 Hard Case	\$36.75
BMP21-MAGNET	Magnet Only Accessory	\$15.75
BMP21-TOOL	Multi-functional Tool Accessory*	\$31.50
BMP21-AC	BMP21 AC Adapter	\$42.00

* Tool accessory includes magnet, flashlight, polestrap, stand and beltloop



Online Video:
www.BradyID.com/bmp21

Indoor/Outdoor Grade Vinyl Tape

B-595 - Super-tough vinyl tape – perfect for voice, data, audio, video, HVAC control, bins, safety and electrical applications

Note: As of March 2011, B-580 material has been replaced by B-595 material. The updated part numbers are shown in table below.

For example: part number "M21-375-580-WT" has become "M21-375-595-WT"



	Black	Black	White	White	White	Black	
Material	Black/White	Black/Yellow	White/Red	White/Blue	White/Green	Black/Orange	Price
3/8" x 21' (9mm x 6.4m)	M21-375-595-WT	M21-375-595-YL	M21-375-595-RD	M21-375-595-BL	M21-375-595-GN	M21-375-595-OR	\$20.46
1/2" x 21' (12mm x 6.4m)	M21-500-595-WT	M21-500-595-YL	M21-500-595-RD	M21-500-595-BL	M21-500-595-GN	M21-500-595-OR	\$20.46
3/4" x 21' (18mm x 6.4m)	M21-750-595-WT	M21-750-595-YL	M21-750-595-RD	M21-750-595-BL	M21-750-595-GN	M21-750-595-OR	\$23.70



Self-Laminating Vinyl

B-427 - Continuous Black on White Self-Laminating Wire Marker

Catalog #	Size	Price
M21-750-427*	.75"x14'	\$27.46
M21-1000-427*	1"x14'	\$33.60
M21-1250-427*	1.25"x14'	\$33.86
M21-1500-427*	1.5"x14'	\$34.26



PermaSleeve[®] Wire Marker Sleeves

B-342 - Continuous Cut-to-Length Heat Shrinkable Sleeves

Catalog #	Size	Price
M21-125-C-342*	.125"x7'	\$41.72
M21-187-C-342	.187"x7'	\$45.52
M21-250-C-342	.250"x7'	\$52.07
M21-375-C-342	.375"x7'	\$57.46



Nylon Cloth

B-499 - For wire, cable, patch panels and faceplates

Catalog #	Size	Price
M21-375-499	.375"x16'	\$22.11
M21-500-499	.5"x16'	\$22.11
M21-750-499	.75"x16'	\$25.00

B-499 - For terminal blocks

Catalog #	Size	Price
M21-375-499-TB	.375"x16'	\$22.11
M21-500-499-TB	.5"x16'	\$22.11



Polyester

B-423 - Black on white for instruments, racks and bins

Catalog #	Size	Price
M21-375-423	.375"x21'	\$19.39
M21-500-423	.5"x21'	\$19.39
M21-750-423	.75"x21'	\$21.54

B-430 - Black on clear for instruments, racks and bins

Catalog #	Size	Price
M21-375-430	.375"x21'	\$19.58
M21-500-430	.5"x21'	\$19.58
M21-750-430	.75"x21'	\$21.75

BMP21[®] and ID Pal[™] label cartridges can be used in either the BMP21 Label Printer or the ID PAL Printer except for those denoted by an asterisk



Did You Know?

These consumables are compatible with the ID Pal[™] Label Printer.

TLS 2200® Thermal Label Printer

www.BradyID.com/tls2200



- Permanent, Quick, Crisp Labels
- Built-in Electrical and Voice/Data Symbols
- Autotext Sizing TLS 2200® reads your label size and style, selects the most suitable type size, and instantly registers it for printing
- Variable Font Sizes from 1 (4 point) to 19 (72 point)


TLS 2200® & Accessories

Catalog #	Description	Price
TLS2200	Printer*	\$795.00
R4310	Black Ribbon	\$29.02
R6010	Black Ribbon	\$29.02
R6210	Black Ribbon	\$29.02
TLS2200-AC	AC Power Supply	\$123.83
TLSTM-QUICKCH	Battery Quick Charger	\$121.26

*Includes hard case, battery pack, battery charger, test labels (PTL-19-423), R6210 ribbon, cleaning strip, communications cable, manual and Quick Start Guide.




Online Video:
www.BradyID.com/tls2200



General Adhesive Wire & Cable Markers

- Industrial strength Vinyl Cloth (B498) and Nylon Cloth (B499) designed to conform to curved surfaces
- Printer automatically calibrates label and prints multiple lines of wire code legend

Wire Gauge	Material	Part Number	Labels/ Roll	Label Dimensions		Maximum Characters/ Line For Font:			Maximum Lines Of Text For Font:			Price
				Inch (mm)	Inch (mm)	2	7	10	2	7	10	
16 to 22	Vinyl Cloth	PTL-7-498	500	0.500 (12.70)	0.500 (12.70)	11	5	3	5	2	1	\$49.20
10 to 16	Vinyl Cloth	PTL-10-498	750	0.250 (6.35)	0.750 (19.05)	5	2	1	3	1	1	\$51.28
10 to 16	Vinyl Cloth	PTL-11-498	500	0.500 (12.70)	0.750 (19.05)	11	5	3	8	4	2	\$44.76
10 to 12	Vinyl Cloth	PTL-16-498	500	0.375 (9.52)	1.000 (25.40)	8	3	2	10	5	3	\$53.78
10 to 12	Nylon Cloth	PTL-16-499	500	0.375 (9.52)	1.000 (25.40)	8	3	2	10	5	3	\$54.70
10 to 12	Vinyl Cloth	PTL-17-498	500	0.500 (12.70)	1.000 (25.40)	11	5	3	3	1	1	\$56.52
10 to 12	Vinyl Cloth	PTL-18-498	250	0.750 (19.05)	1.000 (25.40)	18	7	5	10	5	3	\$37.53
10 to 12	Nylon Cloth	PTL-18-499	250	0.750 (19.05)	1.000 (25.40)	18	7	5	10	5	3	\$37.82
10 to 12	Vinyl Cloth	PTL-19-498	250	1.000 (25.40)	1.000 (25.40)	24	10	7	10	5	3	\$40.18
10 to 12	Nylon Cloth	PTL-19-499	250	1.000 (25.40)	1.000 (25.40)	24	10	7	10	5	3	\$41.09
4 to 10	Vinyl Cloth	PTL-28-498	750	0.250 (6.35)	1.500 (38.10)	5	2	1	16	8	5	\$52.21
4 to 10	Nylon Cloth	PTL-28-499	750	0.500 (12.70)	0.500 (12.70)	5	2	1	16	8	5	\$53.52
4 to 10	Vinyl Cloth	PTL-29-498	500	0.500 (12.70)	0.500 (12.70)	11	5	3	16	8	5	\$49.98
4 to 10	Nylon Cloth	PTL-29-499	500	0.500 (12.70)	1.500 (38.10)	11	5	3	16	8	5	\$51.02
4 to 10	Vinyl Cloth	PTL-30-498	250	0.750 (19.05)	1.500 (38.10)	18	7	5	16	8	5	\$43.97
4 to 10	Nylon Cloth	PTL-30-499	250	0.750 (19.05)	1.500 (38.10)	18	7	5	16	8	5	\$45.16
4 to 10	Vinyl Cloth	PTL-31-498	250	1.000 (25.40)	1.500 (38.10)	24	10	7	16	8	5	\$51.02
4 to 10	Nylon Cloth	PTL-31-499	250	1.000 (25.40)	1.500 (38.10)	24	10	7	16	8	5	\$52.34
Lg. Cable	Vinyl Cloth	PTL-21-498	100	1.000 (25.40)	2.500 (63.50)	24	10	7	23	14	9	\$32.84
Lg. Cable	Vinyl Cloth	PTL-23-498	100	1.000 (25.40)	4.000 (101.60)	24	10	7	23	22	15	\$39.26
Lg. Cable	Vinyl Cloth	PTL-34-498	50	1.500 (38.10)	6.000 (152.40)	37	15	10	64	32	21	\$43.84



Self-Laminating Adhesive Wire & Cable Markers

- Extra-durable B427 material features a clear trailer that wraps over print area to protect the printed text
- Exceptional adhesion to Cat. 5 cable and electrical wires and cable

Application	Material	Part Number	Labels/ Roll	Label Dimensions			Max. Characters/ Line For Font:			Max. Lines Of Text For Font:			Price
				Inch (mm)	Inch (mm)	Inch (mm)	2	7	10	2	7	10	
2 pair Fiber, Single/Multi-Mode	Vinyl Self-lam.	PTL-19-427	250	1.000 (25.40)	1.000 (25.40)	0.375 (9.53)	24	10	7	3	1	1	\$35.73
25 pair Copper, 4-12 pair Fiber	Vinyl Self-lam.	PTL-21-427	100	1.000 (25.40)	2.500 (63.50)	0.750 (19.05)	24	10	7	8	4	2	\$27.36
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-64-427	100	1.000 (25.40)	3.375 (85.73)	1.125 (28.58)	24	10	7	12	12	8	\$16.75
50 pair Copper, 24 pair Fiber	Vinyl Self-lam.	PTL-23-427	100	1.000 (25.40)	4.000 (101.60)	1.000 (25.40)	24	10	7	10	5	3	\$32.58
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-29-427	500	0.500 (12.70)	1.500 (38.10)	0.500 (12.70)	11	5	3	5	2	1	\$48.67
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-30-427	250	0.750 (19.05)	1.500 (38.10)	0.500 (12.70)	18	7	5	5	2	1	\$36.25
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-31-427	250	1.000 (25.40)	1.500 (38.10)	0.500 (12.70)	24	10	7	5	2	1	\$45.85
CAT-5, 4 pair UTP Copper	Vinyl Self-lam.	PTL-32-427	250	1.500 (38.10)	1.500 (38.10)	0.500 (12.70)	37	15	10	5	2	1	\$47.36
50 pair Copper, 24 pair Fiber	Vinyl Self-lam.	PTL-33-427	100	1.500 (38.10)	4.000 (101.60)	1.000 (25.40)	37	15	10	10	5	3	\$44.09
100 pair Copper, 36 pair Fiber	Vinyl Self-lam.	PTL-34-427	50	1.500 (38.10)	6.000 (152.40)	1.500 (38.10)	37	15	10	16	8	5	\$36.51

NEW!

Have you checked out the next generation of Brady printers? - the NEW BMP®71 Label Printer!
Visit www.BradyID.com/bmp71 for view page 104 for more information.




TLS 2200[®] Thermal Label Printer

www.BradyID.com/tls2200

PermaSleeve[™] Wire Marker Sleeves

- Full Circle heat-shrinkable PermaSleeves are made of white polyolefin (3:1 shrink ratio)
- Withstands temps from -65°F to 221°F
- Flame-retardant and Self-extinguishing
- Meets MIL-2305315 (Class 1) Standard



Fits Wire Diameter		Approx. Wire Gauge	Part Number	Sleeves/Roll	Sleeve Dimensions		Max. Characters/Line For Font:			Max. Lines Of Text For Font:			Price
Inch (mm) Min	Inch (mm) Max				Inch (mm) A	Inch (mm) B	2	7	10	2	7	10	
0.023 (0.58)	0.080 (2.03)	28-18	PSPT-094-1-WT	100	1.015 (25.78)	0.182 (4.63)	22	0	0	1	0	0	\$45.67
0.046 (1.17)	0.110 (2.79)	22-16	PSPT-125-1-WT	100	1.015 (25.78)	0.235 (5.96)	22	0	0	1	0	0	\$48.41
0.062 (1.57)	0.150 (3.81)	18-12	PSPT-187-1-WT	100	1.015 (25.78)	0.335 (8.50)	22	9	0	2	1	0	\$53.91
0.094 (2.39)	0.215 (5.46)	16-10	PSPT-250-1-WT	100	1.015 (25.78)	0.439 (11.15)	22	9	6	3	1	1	\$65.30
0.125 (3.18)	0.320 (8.13)	12-6	PSPT-375-1-WT	100	1.015 (25.78)	0.645 (16.38)	22	9	6	5	2	1	\$96.19
0.187 (4.75)	0.450 (11.43)	8-1	PSPT-500-1-WT	100	1.015 (25.78)	0.851 (21.62)	22	9	6	3	1	1	\$111.21
1.015 (25.78)	0.950 (24.13)	1-500	PSPT-1000-1-WT	50	1.015 (25.78)	1.660 (42.16)	22	9	6	16	8	5	\$76.82
0.046 (1.17)	0.110 (2.79)	22-16	PSPT-125-175-WT	100	1.765 (44.83)	0.235 (5.96)	41	0	0	1	0	0	\$65.03
0.062 (1.57)	0.150 (3.81)	18-12	PSPT-187-175-WT	100	1.765 (44.83)	0.335 (8.50)	41	17	11	3	1	1	\$72.22
0.094 (2.39)	0.215 (5.46)	16-10	PSPT-250-175-WT	100	1.765 (44.83)	0.439 (11.15)	41	17	11	3	1	1	\$87.93
0.125 (3.18)	0.320 (8.13)	12-6	PSPT-375-175-WT	100	1.765 (44.83)	0.645 (16.38)	41	17	11	5	2	1	\$129.40
0.187 (4.75)	0.450 (11.43)	8-1	PSPT-500-175-WT	100	1.765 (44.83)	0.851 (21.16)	41	17	11	7	3	2	\$149.54
0.450 (11.43)	0.950 (24.13)	1-500	PSPT-1000-175-WT	50	1.765 (44.83)	1.660 (42.16)	41	17	11	16	8	5	\$104.04

Terminal Block, Patch Panel & Face Plate Labels

- Use individual labels or continuous tape





Diagram	Part Number	Labels/Roll	Polyester Material Color	Label Dimensions		Application	Max. Char./Per Line	Max. Lines/Label	Price
				Inch (mm) A	Inch (mm) B				
■	PTL-7-422	500	White	0.500 (12.70)	0.500 (12.7 m)	Patch panel & face plates—label ea. port	11	5	\$42.20
■	PTL-7-430	500	Clear	0.500 (12.70)	0.500 (12.7 m)	Patch panel & face plates—label ea. port	11	5	\$39.50
○	PTL-46-422	1	White	0.375 (9.50)	50 ft (15.2 m)	Patch panel & face plates—cont. tape, cut-to-size	50	3	\$58.52
○	PTL-46-430	1	Clear	0.375 (9.50)	50 ft (15.2 m)	Patch panel & face plates—cont. tape, cut-to-size	50	3	\$54.57
○	PTL-8-422	1	White	0.500 (12.70)	50 ft (15.2 m)	Patch panel & face plates—cont. tape, cut-to-size	50	5	\$58.52
○	PTL-8-430	1	Clear	0.500 (12.70)	50 ft (15.2 m)	Patch panel & face plates—cont. tape, cut-to-size	50	5	\$54.57
●	PTLTB-498-240	1	White	0.240 (6.10)	30 ft (9.1 m)	Terminal blocks—cont. tape, cut-to-size	5	N/A	\$42.39
●	PTLTB-498-318	1	White	0.318 (8.08)	30 ft (9.1 m)	Terminal blocks—cont. tape, cut-to-size	7	N/A	\$43.56
●	PTLTB-498-375	1	White	0.375 (9.53)	30 ft (9.1 m)	Terminal blocks—cont. tape, cut-to-size	8	N/A	\$44.24

General Industrial Labels

- White polyester with permanent adhesive



Part Number	Labels/Roll	Label Dimensions		Max. Char./Per Line	Max. Lines/of Text	Maximum Bar Code Characters	Price
		Inch (mm) A	Inch (mm) B				
PTL-5-42	750	0.500 (12.70)	0.200 (5.08)	13	2	0	\$38.52
PTL-6-423	750	0.500 (12.70)	0.275 (6.99)	13	3	0	\$40.51
PTL-7-423	500	0.500 (12.70)	0.500 (12.70)	13	5	0	\$35.64
PTL-9-423	750	0.650 (16.51)	0.200 (5.08)	18	2	2	\$42.74
PTL-10-423	750	0.750 (19.05)	0.250 (6.35)	20	2	2	\$44.05
PTL-13-423	750	0.900 (22.86)	0.250 (6.35)	25	2	4	\$46.95
PTL-15-423	750	1.000 (25.40)	0.275 (6.98)	28	2	4	\$51.27
PTL-16-423	500	1.000 (25.40)	0.375 (9.52)	28	4	4	\$42.20
PTL-17-423	500	1.000 (25.40)	0.500 (12.70)	50	5	8	\$42.20
PTL-19-423	250	1.000 (25.40)	1.000 (25.40)	28	12	4	\$29.85
PTL-20-423	100	2.000 (50.80)	1.000 (25.40)	52	12	11	\$23.79
PTL-26-423	100	2.750 (69.85)	1.250 (31.75)	50	13	18	\$34.57
PTL-28-423	750	1.500 (38.10)	0.250 (6.35)	42	2	8	\$61.53
PTL-29-423	500	1.500 (38.10)	0.500 (12.70)	42	5	8	\$47.19
PTL-37-423	100	3.000 (76.20)	1.900 (48.26)	50	22	20	\$34.57
PTL-38-423	100	4.000 (101.60)	1.900 (48.26)	50	22	25	\$41.29

Pre-printed arc flash headers for TLS 2200



Catalog No.	Size HxW (mm)	Header	Price
PTL-37-483-DANGER	1.9" x 3.0" (48.26 x 76.20)	Danger	\$48.07
PTL-37-483-WARNING	1.9" x 3.0" (48.26 x 76.20)	Warning	\$48.07
PTL-38-483-DANGER	1.9" x 4.0" (48.26 x 101.60)	Danger	\$57.76
PTL-38-483-WARNING	1.9" x 4.0" (48.26 x 101.60)	Warning	\$57.76

Raised Panel Labels for TLS 2200



Diagram	Catalog No.	Color	Size (H x W)		Hole Size (mm)	Qty.	Price
			inch	mm			
A 167	PTLEP-167-593	WHITE	1.5 x 1.2	38.1 x 30.5	22.5	100	\$96.34
	PTLEP-167-593-BK	BLACK	1.5 x 1.2	38.1 x 30.5	22.5	100	\$96.34
	PTLEP-167-593-GN	GREEN	1.5 x 1.2	38.1 x 30.5	22.5	100	\$96.34
	PTLEP-167-593-RD	RED	1.5 x 1.2	38.1 x 30.5	22.5	100	\$96.34
	PTLEP-167-593-YL	YELLOW	1.5 x 1.2	38.1 x 30.5	22.5	100	\$96.34
B 168	PTLEP-168-593	WHITE	1.9 x 1.2	48.3 x 30.5	22.5	100	\$107.05
	PTLEP-168-593-BK	BLACK	1.9 x 1.2	48.3 x 30.5	22.5	100	\$107.05
	PTLEP-168-593-GN	GREEN	1.9 x 1.2	48.3 x 30.5	22.5	100	\$107.05
	PTLEP-168-593-RD	RED	1.9 x 1.2	48.3 x 30.5	22.5	100	\$107.05
	PTLEP-168-593-YL	YELLOW	1.9 x 1.2	48.3 x 30.5	22.5	100	\$107.05
C 169	PTLEP-169-593	WHITE	1.8 x 1.8	45.7 x 45.7	30.5	100	\$113.48
	PTLEP-169-593-BK	BLACK	1.8 x 1.8	45.7 x 45.7	30.5	100	\$113.48
	PTLEP-169-593-GN	GREEN	1.8 x 1.8	45.7 x 45.7	30.5	100	\$113.48
	PTLEP-169-593-RD	RED	1.8 x 1.8	45.7 x 45.7	30.5	100	\$113.48
	PTLEP-169-593-YL	YELLOW	1.8 x 1.8	45.7 x 45.7	30.5	100	\$113.48
D 171	PTLEP-171-593	WHITE	0.49 x 1.06	12.5 x 27	n/a	200	\$107.05
	PTLEP-171-593-BK	BLACK	0.49 x 1.06	12.5 x 27	n/a	200	\$107.05
	PTLEP-171-593-GN	GREEN	0.49 x 1.06	12.5 x 27	n/a	200	\$107.05
	PTLEP-171-593-RD	RED	0.49 x 1.06	12.5 x 27	n/a	200	\$107.05
	PTLEP-171-593-SL	SILVER	0.49 x 1.06	12.5 x 27	n/a	200	\$107.05
E 173	PTLEP-173-593	WHITE	1 x 2	25.4 x 50.8	n/a	100	\$81.35
	PTLEP-173-593-BK	BLACK	1 x 2	25.4 x 50.8	n/a	100	\$81.35
	PTLEP-173-593-GN	GREEN	1 x 2	25.4 x 50.8	n/a	100	\$81.35
	PTLEP-173-593-RD	RED	1 x 2	25.4 x 50.8	n/a	100	\$81.35
	PTLEP-173-593-SL	SILVER	1 x 2	25.4 x 50.8	n/a	100	\$81.35
F 174	PTLEP-174-593	WHITE	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-174-593-BK	BLACK	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-174-593-GN	GREEN	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-174-593-RD	RED	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-174-593-SL	SILVER	1 x 4	25.4 x 101.6	n/a	50	\$81.35
G 175	PTLEP-175-593	WHITE	1 x 2	25.4 x 50.8	n/a	100	\$81.35
	PTLEP-175-593-BK	BLACK	1 x 2	25.4 x 50.8	n/a	100	\$81.35
	PTLEP-175-593-GN	GREEN	1 x 2	25.4 x 50.8	n/a	100	\$81.35
	PTLEP-175-593-RD	RED	1 x 2	25.4 x 50.8	n/a	100	\$81.35
	PTLEP-175-593-YL	YELLOW	1 x 2	25.4 x 50.8	n/a	100	\$81.35
H 176	PTLEP-176-593	WHITE	1 x 3	25.4 x 76.2	n/a	50	\$64.21
	PTLEP-176-593-BK	BLACK	1 x 3	25.4 x 76.2	n/a	50	\$64.21
	PTLEP-176-593-GN	GREEN	1 x 3	25.4 x 76.2	n/a	50	\$64.21
	PTLEP-176-593-RD	RED	1 x 3	25.4 x 76.2	n/a	50	\$64.21
	PTLEP-176-593-YL	YELLOW	1 x 3	25.4 x 76.2	n/a	50	\$64.21
I 177	PTLEP-177-593	WHITE	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-177-593-BK	BLACK	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-177-593-GN	GREEN	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-177-593-RD	RED	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-177-593-SL	SILVER	1 x 4	25.4 x 101.6	n/a	50	\$81.35
J 178	PTLEP-178-593	WHITE	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-178-593-BK	BLACK	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-178-593-GN	GREEN	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-178-593-RD	RED	1 x 4	25.4 x 101.6	n/a	50	\$81.35
	PTLEP-178-593-YL	YELLOW	1 x 4	25.4 x 101.6	n/a	50	\$81.35

Use with ribbons: R6010 - Black or R4410 - White

TLS 2200 Ribbons

Part Number	Description	Length ft (m)	Price
R4310	R4310 black ribbon	75 ft (22.90 m)	\$29.02
R6010	R6010 black ribbon	75 ft (22.90 m)	\$29.02
R6210	R6210 black ribbon	75 ft (22.90 m)	\$29.02
R4410-BL	R4410 blue ribbon	75 ft (22.90 m)	\$34.30
R4410-RD	R4410 red ribbon	75 ft (22.90 m)	\$34.30
R4410-WT	R4410 white ribbon	75 ft (22.90 m)	\$34.30

B#'s	Material	Series R4310	Series R4410 (colors)	Series R6010	Series ^R6210
109	Tag	●●	●		
321	Polyolefin				●●
342	Polyolefin	●●			
351	Vinyl				●●
352	Vinyl			●●	
353	Paper	●●			
412	Polypropylene				●●
422	Polyester		△△	●●UL/CSA	△△
423	Polyester		△△	●●UL/CSA/AGA	△△
424	Paper	●●			
426	Polyimide	●●			
427	Vinyl	●●UL			△△
428	Polyester	●●UL/CSA/AGA			
430	Polyester		△△	●●UL/CSA	△△
432	Polyester		△△	●●UL/CSA	
433	Polyester		△△	●●UL	
435	Polyester			●●UL/CSA	
439	Vinyl		△△	●●	△△
457	Polyimide			●●UL	
459	Polyester		△△UL	●●UL/CSA	
461	Polyester	●●			△△
473	Polyester			●●UL/CSA	△△
477	Polyimide			●●UL	△△
478	Polyimide			●●UL	
479	Polyimide			●●UL	
483	Polyester		△△	●●UL/CSA	△△
486	Polyester	●●UL/CSA			
488	Polyester	●●UL/CSA/AGA			△△UL/CSA
489	Polyester	●●UL/CSA			
495	PEN			●●UL	
498	Vinyl Cloth	△△			●●
499	Nylon Cloth	●●UL/CSA			△△
7546	Polyester			●●UL/CSA	
7566	Polyester		△△	●●	
7576	Polyester		△△	●●UL	
8425	Polyolefin		△△	●●UL	

●●	Recommended ribbon for use with respective material.
△△	Acceptable ribbon for use with respective material.
UL	These materials are UL recognized with its respective ribbon.
CSA	These materials are CSA approved with its respective ribbon.
UL/CSA	These materials are UL & CSA approved with its respective ribbon.
AGA	These materials are AGA approved.
^	R6210 ribbon included with printers.

IDXPERT™ Handheld Labeler

www.BradyID.com/idxpert

Sign And Label Printers

IDXPERT™
HANDHELD LABELER



Online Video:
www.BradyID.com/idxpert



More Types of Labels

- Colored continuous tapes for equipment ID and safety warnings
- PermaSleeve™ Wire Marker Sleeves
- Self-Laminating wire & cable markers
- Terminal Block and patch panel markers
- Face Plate & Outlet markers
- General-purpose industrial die-cut labels

More Sizes

- Prints from .06" up to 1.25" characters on label stock up to 1.5" wide

More Symbols

- Code 39 and 128 bar codes
- 82 Symbols including electrical, voice/data, safety & protection, warning, and machine & operational

More Brains

- Drop Lock & Go™ Smart Cartridges™
- Pre-calibrated to orient the label correctly
- Print stand-alone or from a PC (with optional Brady LabelMark™ software)
- Memory to store frequently used set-ups

Prints Clean & Fast

- Users of dot-matrix printers will benefit from crisp, non-smearing thermal transfer print quality, faster print speed and more text-editing and symbols capabilities

Less Waste

- Edge-to-edge printing on continuous tapes so you don't pay for unused label material
- Die-cut labels are pre-cut to the size you need
- Runs on 6 AAs or optional AC power supply

Catalog No.	Description	Price
XPERT-ABC	Printer* (ABC Layout)	\$399.95
XPERT-HC-ABC	Hard Case for ABC Layout	\$75.00
XPERT-KEY	Printer* (KEYBOARD Layout)	\$399.95
XPERT-CONT	Continuous Only Printer	\$250.00
XPERT-HC-KEY	Hard Case for KEYBOARD Layout	\$75.00
XPERT-AC	AC Adapter	\$42.00
LABXPERT-SER-USB	Serial-to-USB adapter for PC cable	\$37.84
PCCABLE-1	Spare PC Cable for Upgrades Only	\$18.87
PCK-4	Cleaning Kit	\$27.56
LM5STDE	LabelMark™5 Software (single user)	\$199.00
XPERT-ABC-KIT-LM	Printer* (ABC Layout) and LabelMark™5 Standard Software Kit	\$641.00
XPERT-KEY-KIT-LM	Printer* (Keyboard Layout) and LabelMark™5 Standard Software Kit	\$641.00

* Printer ships with: Hard Case, 1.5" Continuous Sample Roll Tape, PC cable, Product CD

Indoor/Outdoor Grade Facility & Safety Labels

This indoor/5 year outdoor vinyl is very pliable and conforms well to smooth or rough surfaces such as pipes, walls, doors, panels, shelving, bins and equipment. Excellent resistance to oils, detergents, dirt, grime and many solvents.

- B-595 Indoor/Outdoor Vinyl material
- Permanent adhesive, good for rough surfaces
- Temp Range -40°F to 248°F (-40C to 120C)

Note: As of March 2011, B-580 material has been replaced by B-595 material. The updated part numbers are shown in this table.

For example: part number "XC-750-580-WT-BK" has become "XC-750-595-WT-BK"





Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color	Price
			A	B	A	B		
⊕	XC-375-499	1 roll (cont.)	20 ft.	0.375	9.14m	9.525mm	BK on WT	\$54.87
⊕	XC-500-499	1 roll (cont.)	20 ft.	0.500	9.14m	12.700mm	BK on WT	\$57.06
⊕	XC-750-499	1 roll (cont.)	20 ft.	0.750	9.14m	19.050mm	BK on WT	\$59.33
⊕	XC-1000-499	1 roll (cont.)	20 ft.	1.000	9.14m	24.400mm	BK on WT	\$61.18
⊕	XC-750-595-WT-BK	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	BK on WT	\$55.06
⊕	XC-750-595-OR-BK	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	BK on O	\$55.06
⊕	XC-750-595-YL-BK	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	BK on YL	\$55.06
⊕	XC-750-595-CL-BK	1 roll (cont.)	25 ft.	0.750	9.14m	19.050mm	BK on CL	\$45.90
⊕	XC-750-595-WT-RD	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	WH on RD	\$55.06
⊕	XC-750-595-GN-WT	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	WH on GN	\$55.06
⊕	XC-750-595-BL-WT	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	WH on BL	\$55.06
⊕	XC-750-595-RD-WT	1 roll (cont.)	30 ft.	0.750	9.14m	19.050mm	RD on WT	\$55.06
⊕	XC-500-595-WT-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	BK on WT	\$45.07
⊕	XC-1000-595-WT-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	BK on WT	\$56.07
⊕	XC-1500-595-WT-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	BK on WT	\$67.02
⊕	XC-500-595-OR-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	BK on OR	\$45.07
⊕	XC-1000-595-OR-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	BK on OR	\$56.70
⊕	XC-1500-595-OR-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	BK on OR	\$67.02
⊕	XC-500-595-YL-BK	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	BK on YL	\$45.07
⊕	XC-1000-595-YL-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	BK on YL	\$56.70
⊕	XC-1500-595-YL-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	BK on YL	\$67.02
⊕	XC-500-595-CL-BK	1 roll (cont.)	25 ft.	0.500	9.14m	12.70mm	BK on CL	\$45.07
⊕	XC-1000-595-CL-BK	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	BK on CL	\$56.70
⊕	XC-1500-595-CL-BK	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	BK on CL	\$67.02
⊕	XC-500-595-RD-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	WT on RD	\$45.07
⊕	XC-1000-595-RD-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	WT on RD	\$56.70
⊕	XC-1500-595-RD-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	WT on RD	\$67.02
⊕	XC-500-595-GN-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	WT on GN	\$45.07
⊕	XC-1000-595-GN-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	WT on GN	\$56.70
⊕	XC-1500-595-GN-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	WT on GN	\$67.02
⊕	XC-500-595-BL-WT	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	WT on BL	\$45.07
⊕	XC-1000-595-BL-WT	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	WT on BL	\$56.70
⊕	XC-1500-595-BL-WT	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	WT on BL	\$67.02
⊕	XC-500-595-WT-RD	1 roll (cont.)	30 ft.	0.500	9.14m	12.70mm	RD on WT	\$45.07
⊕	XC-1000-595-WT-RD	1 roll (cont.)	30 ft.	1.000	9.14m	25.40mm	RD on WT	\$56.70
⊕	XC-1500-595-WT-RD	1 roll (cont.)	30 ft.	1.500	9.14m	38.10mm	RD on WT	\$67.02



Wire & Cable Markers – Self-Laminating

- Printer automatically “multiple repeats” your text in the white print area
- B-427 Vinyl Self-Laminating material, resistant to water, oil, solvents and abrasion
- UL recognized
- Temp range -94°F to 158°F (-70C to 70C)

Diagram ▢



Wire Gauge*	Max Wire Diameter	Diagram	Part Number	Qty. per Cartridge	Dimensions (in.)			Dimensions (mm)			Color	Price
					A	B	C	A	B	C		
16-10 Gauge	.16" (4mm)	▢	XSL-11-427	500	0.500	0.750	0.375	12.70mm	19.05mm	9.53mm	BK on WT	\$48.71
16-10 Gauge	.16" (4mm)	▢	XSL-96-427	250	1.000	0.750	0.375	25.40mm	19.05mm	9.53mm	BK on WT	\$34.76
12-10 Gauge	.21" (5mm)	▢	XSL-17-427	500	0.500	1.000	0.375	12.70mm	25.40mm	9.53mm	BK on WT	\$56.84
12-10 Gauge	.21" (5mm)	▢	XSL-18-427	250	0.750	1.000	0.375	19.05mm	25.40mm	9.53mm	BK on WT	\$39.92
12-10 Gauge	.21" (5mm)	▢	XSL-19-427	250	1.000	1.000	0.375	25.40mm	25.40mm	9.53mm	BK on WT	\$45.07
10-4 Gauge	.27" (7mm)	▢	XSL-102-427	250	0.500	1.250	0.375	12.70mm	31.75mm	9.53mm	BK on WT	\$32.18
10-4 Gauge	.27" (7mm)	▢	XSL-103-427	250	1.000	1.250	0.500	25.40mm	31.75mm	12.70mm	BK on WT	\$51.54
10-4 Gauge	.27" (7mm)	▢	XSL-115-427	250	1.500	1.250	0.500	38.10mm	31.75mm	12.70mm	BK on WT	\$46.37
10-4 Gauge	.32" (8mm)	▢	XSL-29-427	450	0.500	1.500	0.500	12.70mm	38.10mm	12.70mm	BK on WT	\$57.98
10-4 Gauge	.32" (8mm)	▢	XSL-30-427	250	0.750	1.500	0.500	19.05mm	38.10mm	12.70mm	BK on WT	\$43.80
10-4 Gauge	.32" (8mm)	▢	XSL-31-427	250	1.000	1.500	0.500	25.40mm	38.10mm	12.70mm	BK on WT	\$54.12
10-4 Gauge	.32" (8mm)	▢	XSL-31-427-YL-BK	250	1.000	1.500	0.500	25.40mm	38.10mm	12.70mm	BK on YL	\$59.28
10-4 Gauge	.32" (8mm)	▢	XSL-32-427	227	1.500	1.500	0.500	38.10mm	38.10mm	12.70mm	BK on WT	\$60.55
3 Gauge-2/0	.53" (14mm)	▢	XSL-21-427-YL-BK	100	1.000	2.500	0.750	25.40mm	63.50mm	19.05mm	BK on YL	\$39.92
3 Gauge-2/0	.53" (14mm)	▢	XSL-21-427	100	1.000	2.500	0.750	25.40mm	63.50mm	19.05mm	BK on WT	\$36.05
3 Gauge-2/0	.53" (14mm)	▢	XSL-116-427	100	1.500	2.500	0.750	38.10mm	63.50mm	19.05mm	BK on WT	\$36.05
3/0-400 kcmil	.85" (22mm)	▢	XSL-23-427	85	1.000	4.000	1.000	25.40mm	101.60mm	25.40mm	BK on WT	\$46.37
3/0-400 kcmil	.85" (22mm)	▢	XSL-23-427-YL-BK	100	1.000	4.000	1.000	25.40mm	101.60mm	25.40mm	BK on YL	\$50.23
3/0-400 kcmil	.85" (22mm)	▢	XSL-33-427	85	1.500	4.000	1.000	38.10mm	101.60mm	25.40mm	BK on WT	\$57.98
500-900 kcmil	1.3" (33mm)	▢	XSL-34-427	50	1.500	6.000	1.500	38.10mm	152.40mm	38.10mm	BK on WT	\$46.37


*Approx based on AWG for THHN wire



Wire & Cable Markers – Adhesive Wrap-Around

- Printer automatically “multiple repeats” your text for 360° legend
- B-498 Vinyl Cloth Material with special adhesive stays put, but marker can be removed and reapplied if necessary
- UL recognized
- Temp Range -40°F to 175°F (-40C to 70C)

Diagram ★



Wire Gauge*	Max Wire Diameter	Diagram	Part Number	Quantity per Cartridge	Dimensions (in.)		Dimensions (mm)		Color	Price
					A	B	A	B		
22-16 Gauge	.11" (2.8mm)	★	X-7-498	300	0.500	0.500	12.70mm	12.70mm	BK on WT	\$42.10
16-10 Gauge	.16" (4mm)	★	X-11-498	275	0.500	0.750	12.70mm	19.05mm	BK on WT	\$42.18
12-10 Gauge	.21" (5mm)	★	X-163-498	225	0.500	1.000	12.70mm	25.40mm	BK on WT	\$41.42
10-4 Gauge	.32" (8mm)	★	X-162-498	165	0.500	1.500	12.70mm	38.10mm	BK on WT	\$38.06
12-10 Gauge	.21" (5mm)	★	X-19-498	200	1.000	1.000	25.40mm	25.40mm	BK on WT	\$37.14
12-10 Gauge	.21" (5mm)	★	X-18-498	225	0.750	1.000	19.05mm	25.40mm	BK on WT	\$43.37
10-4 Gauge	.27" (7mm)	★	X-103-498	200	1.000	1.250	25.40mm	31.75mm	BK on WT	\$37.96
10-4 Gauge	.32" (8mm)	★	X-31-498	165	1.000	1.500	25.40mm	38.10mm	BK on WT	\$43.67
3 Gauge - 2/0	.53" (14mm)	★	X-21-498	95	1.000	2.500	25.40mm	63.50mm	BK on WT	\$36.96
3/0 - 400Kcmil	.85" (22mm)	★	X-23-498	60	1.000	4.000	25.40mm	101.60mm	BK on WT	\$39.09

*Approx based on AWG for THHN wire




Wire & Cable Markers – PermaSleeve® Sleeves

- B-342 Heat Shrink Material (3:1 shrink ratio)
- Self-extinguishing—meets material & physical properties of MIL-DTL-23053/5C Class 1, MIL-M-81531, MIL-STD-202F, method 215 and UL 224
- Temp Range -67°F to 275°F (-55C to 135C)


Diagram ●

Diagram ◻



Wire Gauge*	Wire Diameter Range	Diagram	Part Number	Quantity per Cartridge	Dimensions (in.)		Dimensions (mm)		Color	Price
					A	B	A	B		
1.015" MARKER LENGTH										
22-16 Gauge	.046-.110" (1.22-2.8mm)	●	XPS-125-1	100	1.015	0.235	25.78mm	5.96mm	BK on WT	\$51.28
18-12 Gauge	.062-.150" (1.6-3.8mm)	●	XPS-187-1	100	1.015	0.335	25.78mm	8.50mm	BK on WT	\$56.29
16-10 Gauge	.094-.215" (2.4-5.5mm)	●	XPS-250-1	100	1.015	0.439	25.78mm	11.15mm	BK on WT	\$67.57
12-6 Gauge	.125-.320" (3.2-8.1mm)	●	XPS-375-1	100	1.015	0.645	25.78mm	16.38mm	BK on WT	\$97.62
CONTINUOUS (CUT TO LENGTH)										
22-16 Gauge	.046-.110" (1.22-2.8mm)	◻	XPS-125-CONT	1 roll (cont.)	8 ft.	0.235	2.45m	5.96mm	BK on WT	\$44.50
22-16 Gauge	.046-.110" (1.22-2.8mm)	◻	XPS-125-CONT-YL-BK	1 roll (cont.)	8 ft.	0.235	2.45m	5.96mm	BK on YL	\$44.50
18-12 Gauge	.062-.150" (1.6-3.8mm)	◻	XPS-187-CONT	1 roll (cont.)	8 ft.	0.335	2.45m	8.5mm	BK on WT	\$48.87
18-12 Gauge	.062-.150" (1.6-3.8mm)	◻	XPS-187-CONT-YL-BK	1 roll (cont.)	8 ft.	0.335	2.45m	8.5mm	BK on YL	\$48.87
16-10 Gauge	.094-.215" (2.4-5.5mm)	◻	XPS-250-CONT	1 roll (cont.)	8 ft.	0.439	2.45m	11.15mm	BK on WT	\$53.79
16-10 Gauge	.094-.215" (2.4-5.5mm)	◻	XPS-250-CONT-YL-BK	1 roll (cont.)	8 ft.	0.439	2.45m	11.15mm	BK on YL	\$53.79
12-6 Gauge	.125-.320" (3.2-8.1mm)	◻	XPS-375-CONT	1 roll (cont.)	8 ft.	0.645	2.45m	16.38mm	BK on WT	\$78.84


*Approx based on AWG for THHN wire



Terminal Block Markers

- These specially designed narrow-width markers automatically set to fixed spacing and separation between leg ends and automatically rotate to top-down orientation for perfect alignment on terminal blocks. Printer can auto-serialize to save additional time. B-428 Vinyl Cloth material.
- Temp Range -40°F to 248°F (-40C to 120C)
- UL Recognized

Diagram ●



Width of Strip	Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color	Price
				A	B	A	B		
.240" wide	●	XC-240-498	1 roll (cont.)	0.240	20 ft.	6.10mm	7.9m	BK on WT	\$53.31
.318" wide	●	XC-318-498	1 roll (cont.)	0.318	20 ft.	8.07mm	7.9m	BK on WT	\$53.59
.375" wide	●	XC-375-498	1 roll (cont.)	0.375	20 ft.	9.53mm	7.9m	BK on WT	\$54.87

Bins & Storage I.D., General Industrial I.D., Component I.D.



A variety of sizes and extra-aggressive adhesives for bins, drawers, tools and equipment and components inside of panels.



B-483 Ultra-Aggressive Polyester

- Permanent adhesive for textured/powder-coated surfaces
- Temp Range -40°F to 248°F (-40C to 120C)
- UL Recognized

B-595 Indoor/Outdoor Vinyl

- Permanent adhesive, good for rough surfaces
- Wide range of colors
- Temp Range -40°F to 248°F (-40C to 120C)

B-428 Metalized Polyester

- Permanent adhesive
- Silver finish
- Temp Range -40°F to 176°F (-40C to 80C)
- UL Recognized
- Works best on flat surfaces

Diagram ▲




Diagram ▲




Diagram ○




Diagram ✖



B-499 Nylon Cloth Material

- Permanent adhesive
- Pliable, for rough or smooth surfaces
- Temp Range -94°F to 194°F (-70C to 90C)
- UL Recognized

B-422 Gloss Polyester

- Permanent adhesive
- For smoother surfaces
- Temp Range -40°F to 212°F (-40C to 100C)
- UL Recognized

Material Notes	Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color	Price
				A	B	A	B		
Permanent Nylon Cloth (round label)	✖	X-82-499	300	.375" dia.		9.53mm dia.		BK on WT	\$38.21
Permanent Nylon Cloth (round label)	✖	X-83-499	300	.500" dia.		12.70mm dia.		BK on WT	\$38.21
Permanent Nylon Cloth	▲	X-11-499	275	0.750	0.500	19.05mm	12.70mm	BK on WT	\$33.22
Permanent Nylon Cloth	▲	X-84-499	250	0.900	0.500	22.86mm	12.70mm	BK on WT	\$34.40
Permanent Nylon Cloth (round label)	▲	X-162-499	165	1.500	0.500	38.10mm	12.70mm	BK on WT	\$36.93
Permanent Nylon Cloth (round label)	▲	X-130-499	300	1.500	0.750	38.10mm	19.05mm	BK on WT	\$36.77
Ultra Polyester for textured surfaces	▲	X-17-483	500	1.000	0.500	25.40mm	12.70mm	BK on WT	\$56.84
Ultra Polyester for textured surfaces	▲	X-61-483	100	2.000	0.500	50.80mm	12.70mm	BK on WT	\$28.33
Ultra Polyester for textured surfaces	▲	X-20-483	100	2.000	1.000	50.80mm	25.40mm	BK on WT	\$36.05
Metalized Polyester	▲	X-17-428-SV-BK	500	1.000	0.500	25.40mm	12.70mm	BK on SV	\$62.55
Metalized Polyester (black border)	▲	X-24-428-SVBB-BK	500	1.130	0.500	28.70mm	12.70mm	BK on SV	\$55.05
Metalized Polyester	▲	X-29-428-SV-BK	500	1.500	0.500	38.10mm	12.70mm	BK on SV	\$71.32
Metalized Polyester	▲	X-30-428-SV-BK	325	1.500	0.750	38.10mm	19.05mm	BK on SV	\$55.94
Metalized Polyester	▲	X-20-428-SV-BK	100	2.000	1.000	50.80mm	25.40mm	BK on SV	\$40.02
Gloss Polyester	▲	X-7-422	350	0.500	0.500	12.70mm	12.70mm	BK on WT	\$39.92
Gloss Polyester	▲	X-30-422	250	1.500	0.750	38.10mm	19.05mm	BK on WT	\$55.40
Gloss Polyester	▲	X-19-422	250	1.000	1.000	25.40mm	25.40mm	BK on WT	\$45.07
Gloss Polyester	▲	X-132-422	250	1.500	1.250	38.10mm	31.75mm	BK on WT	\$60.82
Indoor/Outdoor Vinyl (colored supplies)	○	XC-500-595-YL-BK	1 roll (cont.)	30 ft.	0.500	9.14mm	12.70mm	BK on YL*	\$45.07
Indoor/Outdoor Vinyl (colored supplies)	○	XC-1000-595-YL-BK	1 roll (cont.)	30 ft.	1.000	9.14mm	25.40mm	BK on YL*	\$56.70
Indoor/Outdoor Vinyl (colored supplies)	○	XC-1500-595-YL-BK	1 roll (cont.)	30 ft.	1.500	9.14mm	38.10mm	BK on YL*	\$67.02


*also available in Red, Orange, Green, Blue, White, and Clear



Voice/Data Cable Markers

Ideal for marking data cabling, this cable marker's protected printing offers superior abrasion resistance and resistance to dirt, oils, solvents and water. Marker features a clear, non-printed area which wraps around and overlaminates the printed text. Printer automatically "multiple repeats" your text in the white print area. B-427 Vinyl Self Laminating material.

Diagram ▾



- Resistant to abrasion, water, oil and solvents
- UL recognized
- Temp range -94°F to 158°F (-70C to 70C)

Sized to Fit	Diagram	Part Number	# per Cartridge	Dimensions (in.)			Dimensions (mm)			Color	Price
				A	B	C	A	B	C		
2 pair Fiber/Coaxial, Single/Multi Mode	▾	XSL-19-427	250	1.000	1.000	0.375	25.40mm	25.40mm	9.53mm	BK on WT	\$45.07
CAT-5, 4 pair UTP Copper	▾	XSL-102-427	250	0.500	1.250	0.375	12.70mm	31.75mm	9.53mm	BK on WT	\$32.18
CAT-5, 4 pair UTP Copper, Fiber, Coaxial	▾	XSL-103-427	250	1.000	1.250	0.500	25.40mm	31.75mm	12.70mm	BK on WT	\$51.54
CAT-5, 4 pair UTP Copper	▾	XSL-115-427	250	1.500	1.250	0.500	38.10mm	31.75mm	12.70mm	BK on WT	\$46.37
CAT-5, 4 pair UTP Copper	▾	XSL-29-427	500	0.500	1.500	0.500	12.70mm	38.10mm	12.70mm	BK on WT	\$57.98
CAT-5, 4 pair UTP Copper	▾	XSL-30-427	250	0.750	1.500	0.500	19.05mm	38.10mm	12.70mm	BK on WT	\$43.80
CAT-5, 4 pair UTP Copper, Fiber, Coaxial	▾	XSL-31-427	250	1.000	1.500	0.500	25.40mm	38.10mm	12.70mm	BK on WT	\$54.12
CAT-5, 4 pair UTP Copper, Fiber, Coaxial	▾	XSL-31-427-YL-BK	250	1.000	1.500	0.500	25.40mm	38.10mm	12.70mm	BK on YL	\$59.28
CAT-5, 4 pair UTP Copper, Fiber, Coaxial	▾	XSL-32-427	250	1.500	1.500	0.500	38.10mm	38.10mm	12.70mm	BK on WT	\$60.55
25 pair Copper, 4-12 pair Fiber, Coaxial	▾	XSL-21-427	100	1.000	2.500	0.750	25.40mm	63.50mm	19.05mm	BK on WT	\$36.05
25 pair Copper, 4-12 pair Fiber, Coaxial	▾	XSL-21-427-YL-BK	100	1.000	2.500	0.750	25.40mm	63.50mm	19.05mm	BK on YL	\$39.92
25 pair Copper, 4-12 pair Fiber, Coaxial	▾	XSL-116-427	100	1.500	2.500	0.750	38.10mm	63.50mm	19.05mm	BK on WT	\$36.05
50 pair Copper, 24 pair Fiber, Backbone	▾	XSL-23-427	100	1.000	4.000	1.000	25.40mm	101.60mm	25.40mm	BK on WT	\$46.37
50 pair Copper, 24 pair Fiber, Backbone	▾	XSL-23-427-YL-BK	100	1.000	4.000	1.000	25.40mm	101.60mm	25.40mm	BK on YL	\$50.23
50 pair Copper, 24 pair Fiber, Backbone	▾	XSL-33-427	100	1.500	4.000	1.000	38.10mm	101.60mm	25.40mm	BK on WT	\$57.98
100 pair Copper, 36 pair Fiber, Backbone	▾	XSL-34-427	50	1.500	6.000	1.500	38.10mm	152.40mm	38.10mm	BK on WT	\$46.37



Voice/Data Patch Panel, Outlet & Faceplate Markers

B-422 Gloss Polyester

- Permanent adhesive for smoother surfaces
- Temp Range -40°F to 212°F (-40C to 82C)
- UL Recognized

Diagram ▲





Diagram ○



Application	Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color	Price
				A	B	A	B		
Label Each Port	▲	X-7-422	350	0.500	0.500	12.70mm	12.70mm	BK on WT	\$39.92
Label Punch Blocks or Multiple Ports on Cont. Tape	○	XC-375-422	1 roll (cont.)	30 ft.	0.375	9.14mm	9.53mm	BK on WT	\$55.40
Label Punch Blocks or Multiple Ports on Cont. Tape	○	XC-475-422	1 roll (cont.)	30 ft.	0.475	9.14mm	12.07mm	BK on WT	\$52.26
Label Faceplate	▲	X-17-422	500	1.000	0.500	25.40mm	12.70mm	BK on WT	\$53.34
Label Faceplate	▲	X-29-422	500	1.500	0.500	38.10mm	12.70mm	BK on WT	\$59.15



Voice/Data I.D. for Racks, Bays, Frames, Public Network & Data Centers

B-422 Gloss Polyester

- Permanent adhesive
- Temp Range -40°F to 212°F (-40C to 100C)
- UL Recognized

B-483 Ultra-Aggressive Polyester

- Permanent adhesive for textured/powder-coated surfaces
- Temp Range -40°F to 248°F (-40C to 120C)
- UL Recognized

B-595 Indoor/Outdoor Vinyl

- Permanent adhesive, good for rough surfaces
- Wide range of colors
- Temp Range -40°F to 248°F (-40C to 82C)

Diagram ▲





Diagram ○



Material Notes	Diagram	Part Number	Labels per Cartridge	Dimensions (in.)		Dimensions (mm)		Color	Price
				A	B	A	B		
Ultra Polyester for textured surfaces	▲	X-17-483	500	1.000	0.500	25.40mm	12.70mm	BK on WT	\$56.84
Ultra Polyester for textured surfaces	▲	X-61-483	100	2.000	0.500	50.80mm	12.70mm	BK on WT	\$28.32
Ultra Polyester for textured surfaces	▲	X-20-483	100	2.000	1.000	50.80mm	25.40mm	BK on WT	\$36.05
Gloss Polyester	▲	X-17-422	500	1.000	0.500	25.40mm	12.70mm	BK on WT	\$53.34
Gloss Polyester	▲	X-29-422	500	1.500	0.500	38.10mm	12.70mm	BK on WT	\$59.15
Gloss Polyester	▲	X-30-422	250	1.500	0.750	38.10mm	19.05mm	BK on WT	\$55.40
Gloss Polyester	▲	X-19-422	250	1.000	1.000	25.40mm	25.40mm	BK on WT	\$45.07
Gloss Polyester	○	XC-1000-422	1 roll (cont.)	30 ft.	1.000	9.14mm	25.40mm	BK on WT	\$64.43
Indoor/Outdoor Vinyl (colored supplies)	○	XC-500-595-YL-BK	1 roll (cont.)	30 ft.	0.500	9.14mm	12.70mm	BK on YL*	\$45.07
Indoor/Outdoor Vinyl (colored supplies)	○	XC-1000-595-YL-BK	1 roll (cont.)	30 ft.	1.000	9.14mm	25.40mm	BK on YL*	\$56.70
Indoor/Outdoor Vinyl (colored supplies)	○	XC-1500-595-YL-BK	1 roll (cont.)	30 ft.	1.500	9.14mm	38.10mm	BK on YL*	\$67.02

*also available in Red, Orange, Green, Blue, White, and Clear

HandiMark® Portable Label Maker

www.BradyID.com/handimark

Sign And Label Printers




Brady continues to manufacture and fully stock the complete range of labels and accessories for the HandiMark® Portable Label Maker!

HandiMark® Printer & Accessories

Catalog #	Description	Price
42006	HandiMark AC Power Supply	\$123.83
42124	HandiMark Quick Charger	\$121.26
42008	Spare Battery (Std. Battery)	\$93.44
42007	Standard Battery Charger	\$44.47
42073	Super Charge (Quick charger and spare battery)	\$210.54
42072	Mega Charge (Quick charger, spare battery and AC Power Supply)	\$334.41
42009	Alcohol Cleaning Strips (5 per pkg.)	\$13.91
49199	Soft Case	\$72.29
42010	Spare Hard Carrying Case	\$83.48
42004	PC Connecting Cable	\$61.94


*Includes rechargeable battery & battery charger, hard carrying case, 1 roll of 2" sample tape, black ribbon, cleaning strip, tutorial and symbols reference chart.

US Patent Numbers: 5,318,370; 5,918,989; 5,951,177; 6,113,293; 6,142,686; D409,230



Industrial Grade Ribbons

- Super-tough, smear-proof, easy-to-load ribbons last for years outdoors.



Size	Catalog #					Price
One size fits all tape widths 2" x 75' (51 mm x 23 m)						
	Black	White	Red	Blue	Green	
	42011	42012	42013	42014	42015	\$33.44



Outdoor Grade Vinyl Tape (B-595)

Labels adhere well to pipes, walls, equipment, doors – most clean, dry surfaces.

- Withstands temperatures from 180°F to -40°F

Description	Catalog Number										Price
1/2" x 50' (13 mm x 15.2 m)	142269	142302	142272	142275	142278	142281	142284	142287	142290	142296	\$47.45
1" x 50' (25 mm x 15.2 m)	142270	142303	142273	142276	142279	142282	142285	142288	142291	142297	\$66.19
2" x 50' (51 mm x 15.2 m)	142271	142304	142274	142277	142280	142283	142286	142289	142292	142298	\$99.33

Reflective Tape (B-584)

- Suitable for indoor or outdoor use
- Reflective capabilities are ideal for reading labels in low light conditions with a flashlight or from a vehicle
- Applications include utility pole and box labeling, door labeling, labeling rooftop equipment and equipment that needs to be viewed from a road side



Repositionable Vinyl Tape (B-581)

- Vinyl tape has a special adhesive that allows easy removal of label to reapply again...and again
- Best choice for indoor marking where frequent repositioning is required, such as shelves



Description	Catalog Number			
	Reflective Silver	Reflective Orange	Reflective Yellow	Price
Size				
1" x 33' (25 mm x 10 m)	42062	42066	42064	\$113.74
2" x 33' (51 mm x 10 m)	42063	42067	42065	\$164.16

Description	Catalog Number		
	Yellow	White	Price
Size			
1/2" x 50' (13 mm x 15.2 m)	42103	42100	\$50.36
1" x 50' (25 mm x 15.2 m)	42104	42101	\$70.52
2" x 50' (51 mm x 15.2 m)	42105	42102	\$106.53

Economy Polypropylene Tape (B-529)

- Ideal, low-cost label
- For use indoors on smooth, flat surfaces
- Available in three sizes, white only



Size	Catalog Number		
	White	Price	
1/2" x 50' (13 mm x 15.2 m)	42068	\$40.26	
1" x 50' (25 mm x 15.2 m)	42069	\$51.79	
2" x 50' (51 mm x 15.2 m)	42071	\$71.97	

Tamper Resistant Tape (B-530)

- Tape destructs into tiny fragments when tampered with, making removal very tedious and difficult
- White only



Size	Catalog Number		
	White	Price	
1/2" x 50' (13 mm x 15.2 m)	42137	\$57.55	
1" x 50' (25 mm x 15.2 m)	42138	\$76.28	
2" x 50' (51 mm x 15.2 m)	42139	\$113.74	

NEW!

Did You Know? The new BMP®71 Label Printer

Have you checked out the next generation of Brady printers? - the NEW BMP®71 Label Printer! The best features and functionalities of Brady's portable label printers are now combined into one easy-to-use, top-of-the-line portable thermal transfer printer

Visit www.BradyID.com/bmp71 for view page 104 for more information.




I.D. PRO[®] PLUS PRINTER ACCESSORIES

www.BradyID.com

I.D. PRO[®] Plus
WIRE MARKER PRINTER

Brady continues to manufacture and fully stock the complete range of labels, sleeves and accessories for the I.D. Pro[™] Plus Printer!



U.S. Patent Number D409,230

Description	Part#	Price
Hard Side Carrying Case	IDPRO-HC	\$49.07
12-volt Battery Charger	IDPRO-BG12V	\$27.80
Battery Pack	IDPRO-BP	\$49.07
Battery Charger	IDPRO-BC	\$22.05
Black High-Performance Ribbon for PermaSleeve [™] and DuraSleeve [™]	R5300	\$113.68
Black High-Performance Ribbon for all labels and BradySleeve [™] (Lighter Print more Smear resistant)	R7300	\$13.68

Sign And Label Printers



Adhesive Wire Marking Labels for I.D. Pro[®] Plus

- Labels are designed for use with the I.D. Pro[™] Plus Portable Printer
- Highly durable and easily visible; perfect for all your on-site label or wire marking applications

Label Material	Labels per Roll	Approx. Wire Gauge	Label Dimensions Inch (mm)		Max. Lines of Print	Maximum Characters Across		Part#	Price
			Width	Height		Large	Small		
Nylon Cloth, Permanent Adhesive	500	16-22	.5(12.7)	.5(12.7)	3	3	4	WML-305-499	\$59.84
General-Purpose Vinyl Cloth	500	16-22	.5(12.7)	.5(12.7)	3	3	4	WML-305-502	\$58.59
Nylon Cloth, Permanent Adhesive	250	10-16	.5(12.7)	.75(19.05)	4	3	4	WML-505-499	\$37.80
General-Purpose Vinyl Cloth	250	10-16	.5(12.7)	.75(19.05)	4	3	4	WML-505-502	\$37.00
Nylon Cloth, Permanent Adhesive	250	10-16	1.0(25.4)	.75(19.05)	4	7	10	WML-511-499	\$45.15
General-Purpose Vinyl Cloth	250	10-16	1.0(25.4)	.75(19.05)	4	7	10	WML-511-502	\$44.26
Nylon Cloth, Permanent Adhesive	250	10-12	.5(12.7)	1.0(25.4)	6	3	4	WML-705-499	\$40.63
General-Purpose Vinyl Cloth	250	10-12	.5(12.7)	1.0(25.4)	6	3	4	WML-705-502	\$39.84
Nylon Cloth, Permanent Adhesive	250	10-12	1.0(25.4)	1.0(25.4)	6	7	10	WML-711-499	\$48.66
General-Purpose Vinyl Cloth	250	10-12	1.0(25.4)	1.0(25.4)	6	7	10	WML-711-502	\$48.13
General-Purpose Vinyl Cloth	250	6-10	.5(12.7)	1.25(31.75)	8	3	4	WML-905-502	\$43.23
Nylon Cloth, Permanent Adhesive	250	6-10	1.0(25.4)	1.25(31.75)	8	7	10	WML-911-499	\$52.68
General-Purpose Vinyl Cloth	250	6-10	1.0(25.4)	1.25(31.75)	8	7	10	WML-911-502	\$51.34

Self-Laminating Wire Marker Labels for I.D. Pro[®] Plus

- Vinyl labels feature clear "trailer" that wraps to protect printed text
- Resistant to oil, water, and solvents



Approx. Wire Gauge	Max. Wire Diameter Inch (mm)	Label Dimensions Inch (mm)		Write-on Area Height	Lines of Print	Max. Characters Across		Part#	Price Each
		Width	Height			Large	Small		
10-12	.21(5.3)	.5(12.7)	1.0(25.4)	.375(9.53)	2	3	4	WML-205-292-1	\$33.95
10-14	.185(4.7)	.5(12.7)	.75(19.05)	.4(10.16)	2	3	4	WML-205-292-2S*	\$49.34
10-16	.16(4.1)	.5(12.7)	.75(19.05)	.375(9.53)	2	3	4	WML-205-292-75	\$28.51
10-12	.21(5.3)	1.0(25.4)	1.0(25.4)	.375(9.53)	2	7	10	WML-211-292-1	\$41.81
10-16	.16(4.1)	1.0(25.4)	.75(19.05)	.375(9.53)	2t	7	10	WML-211-292-75	\$37.71
6-10	.26(6.6)	.50(12.7)	1.25(31.75)	.5(12.7)	3	3	4	WML-305-292	\$33.76
6-10	.26(6.6)	.50(12.7)	1.25(31.75)	.52(13.21)	3	3	4	WML-305-292-2S*	\$56.57
6-10	.26(6.6)	1.0(25.4)	1.25(31.75)	.5(12.7)	3	7	10	WML-311-292	\$45.42
6-10	.26(6.6)	1.5(38.1)	1.25(31.75)	.5(12.7)	3	10	15	WML-317-292	\$53.60

*Labels are scored in half, length-wise. The width is only .25"



BradySleeve™ Wire Marking Sleeves

- Exclusive topcoat “soaks up” ink & retains it permanently, without additional curing
- Durable BradySleeve markers stand up to tough conditions 500 per roll

Approx. Wire Gauge	Range of Wire Diameter		Sleeve Dimensions Inch (mm)		Max. Lines of Print	Max. Characters Across			Part#	Price
	Min.	Max.	Width	Height		Large	Small			
12-18	.075(1.90)	.13(3.30)	1.0(25.40)	3.5(8.90)	1	7	10	WMS-111-321	\$272.85	

Multiple-Across Wire Marking Strips

- Approx. wire gauge - 10-14

Label Material	Number of Strips Across	Quantity Per Roll Strips/Sets	Label Dimensions Inch (mm)		Max. Lines of Print	Max. Characters Across			Part#	Price
			Width	Height		Large	Small			
Nylon Cloth	2	500-250	.5(12.7)	.75(19.05)	4	3	4	WML-505-499-2S*	\$54.67	
White Vinyl Cloth	2	500/250	.5(12.7)	.75(19.05)	4	3	4	WML-505-502-2S*	\$53.69	

*Labels are scored in half, length-wise. The width is only .25"



Cable Marking Labels

- Self-Laminating transparent vinyl
- Clear overlaminates is ideal for cable marking applications
- Resistant to oil, water and solvents
- Withstands temperatures from -40°F to 150°F
- Excellent for underground wiring

Labels Per Roll	Label Dimensions Inch (mm)		Write-on Area Height	Max. Lines of Print	Max. Characters Across			Part#	Price
	Width	Height			Large	Small			
100	1.0(25.4)	2.5(63.5)	.75(19.05)	4	7	10	WML-511-292	\$32.13	
100	1.5(38.1)	2.5(63.5)	.75(19.05)	4	10	15	WML-517-292	\$39.83	
100	1.0(25.4)	4.0(101.6)	1.0(25.4)	6	7	10	WML-711-292	\$38.04	
100	1.5(38.1)	4.0(101.6)	1.0(25.4)	6	10	15	WML-717-292	\$51.65	



Component & General Identification Labels

- Suitable for marking components in control panels, electronic components and circuit boards, faceplates and electrical receptacles
- Available in white vinyl cloth with a printable topcoat
- Withstands temperatures from -40°F to 180°F
 - Resistant to oil, water and humidity
 - Leaves no adhesive residue when removed
 - Ideal for permanent or temporary applications

Label Material	Labels per Roll	Label Dimensions Inch (mm)		Maximum Lines of Print	Max. Characters Across			Part#	Price Each
		Width	Height		Large	Small			
Polyester	500	.5(12.7)	.275(7.0)	1	3	4	CL-105-619	\$34.60	
Vinyl Cloth	500	1.0(25.4)	.275(7.0)	1	7	10	CL-111-502	\$53.02	
Tamper-Proof Vinyl	500	1.0(25.4)	.275(7.0)	1	7	10	CL-111-607	\$56.95	
Polyester	500	1.0(25.4)	.275(7.0)	1	7	10	CL-111-619	\$39.50	
Metallized Polyester	500	1.0(25.4)	.275(7.0)	1	7	10	CL-111-969	\$54.74	
Polyester	500	1.0(25.4)	.275(7.0)	1	10	15	CL-117-619	\$47.19	
Vinyl Cloth	500	1.0(25.4)	.50(12.7)	3	7	10	CL-311-502	\$65.70	
Polyester	500	1.0(25.4)	.50(12.7)	3	7	10	CL-311-619	\$51.14	
Metallized Polyester	500	1.0(25.4)	.50(12.7)	3	7	10	CL-311-969	\$68.68	
Polyester	500	1.5(38.1)	.50(12.7)	3	10	15	CL-317-619	\$57.50	
Polyester	250	1.5(38.1)	.75(19.05)	4	10	15	CL-517-619	\$38.08	
Polyester	250	1.5(38.1)	1.25(31.75)	8	10	15	CL-917-619	\$48.35	

MiniMark™ Industrial Label Printer

www.BradyID.com/minimark



The Brady MiniMark™ Industrial Label Printer offers an affordable sign and label making solution that is compact, fast, and incredibly versatile. You won't believe how powerful and easy Brady's MarkWare Express Software is until you try it!

- APPLICATIONS – Signs, Pipe Markers, Equipment ID, Racks & Shelving, and more!
- VERSATILE – Uses continuous tapes for multiple applications
- POWERFUL – Ships with Brady's MarkWare Express Software
- FAST – Prints up to three inches per second
- EASY-LOAD-SUPPLIES – Arrive pre-loaded on spindles with flanges to prevent telescoping tape. Drop-in ease of loading.
- COMPACT – Doesn't take up a lot of space in work areas
- SOFTWARE COMPATABILITY – Ships with MarkWare™ Express Software but can also be used with MarkWare Standard Software and MarkWare Lean Software
- CUTTER – Built-in cutter minimizes waste



MarkWare™ Express Software

Ships with every MiniMark printer.

The ultimate sign and pipe marker database.

MarkWare™ EXPRESS software contains thousands of pre-made pipe markers, OSHA signs, and labels ready to print as-is or customize with a click of your mouse! Fast. Accurate. Amazing!

- Signs, labels, tags, pipe markers and more - all pre-made and ready to print or customize
- Thousands of stock legends
- 1-Click translation of your selected sign or pipemarker into French or Spanish
- High-speed search gives you instant access
- OSHA and ANSI sign formats, ANSI-ASME Pipe Markers



Printer Part Numbers

Catalog No.	Description	Price Each
52041	MiniMark™ Industrial Label Printer (includes Markware Express Software, USB cable, and cleaning kit)	\$1,195.00

Material Starter Packages (Printer Sold Separately)

Catalog No.	Description	Price Each
105089	Supplies Starter Package - General Industrial (Printer Sold Separately) Includes: MarkWare™ software; 2 rolls each of 4" white and yellow vinyl; 2 rolls each of 2.25" white and yellow vinyl; 2 rolls each of 1.125" white and yellow vinyl; and 8 rolls of black ribbon (4 pkgs.) All vinyl is B-595 vinyl.	\$1,845.74
105088	Supplies Starter Package - Pipe Marker (Printer Sold Separately) Includes: MarkWare™ software; 3 rolls of 4" yellow vinyl; 1 roll each of 4" red, green, and blue vinyl; 3 rolls of 2.25" yellow vinyl; 1 roll each of 2.25" red, green, and blue vinyl; 1 roll each of 1.125" yellow, red, green, and blue vinyl; and 6 rolls each of black and white ribbon (3 pkgs. each) All vinyl is B-595 vinyl.	\$2,308.62

Printer Starter Packages - Please see facing page.

MiniMark™ Printer Specifications

- Maximum Printing Width: 4 inches
- Minimum Printing Length: From 1 inch to 39 inches
- Dimensions: 8 inches wide x 10.25 inches deep x 7 inches high
- Weight: 4.85 pounds
- Current – Input: 100-240V / 50 / 60Hz / 1.6A
– Output: 24VDC – 2.5A

Brady 360® Printer Protection & Care Plan

Brady 360 plans provide a printer extended warranty, loaner printer, free firmware upgrades and preventive care needed to extend the life of your MiniMark printer. Sold together with the printer or as a stand-alone plan (purchase of stand-alone plan allowed within 1 month after printer purchase)

Brady 360 Basic Plan – 3 years total warranty coverage and access to a loaner printer if your covered printer is in for service

Brady 360 Preferred Plan – same 3 yrs of warranty and loaner printer, plus one free *Brady 360® Preventive maintenance service*, free printer upgrades and two hours of *Brady 360® Professional Tech Support Services*.

For additional information & details visit www.bradyid.com/brady360

Catalog No.	Description	Price Each
114447	Brady 360 Basic - For Desktop Facility ID Printer	\$350.00
114448	Brady 360 Preferred - For Desktop Facility ID Printer	\$600.00
114453	MiniMark™ Printer with Brady 360 Basic	\$1,545.00
114458	MiniMark™ Printer with Brady 360 Preferred	\$1,795.00

MiniMark PowerValue Packages

Save when you purchase our two most common accessories with your MiniMark printer. Powerful and easy-to-use MarkWare™ Software takes your MiniMark label-making muscle to even higher levels. Add to that the protection of a Brady 360 Basic plan and you'll have the piece of mind knowing that your MiniMark will be ready to work for you whenever you need it.

Catalog No.	Description	Price Each
104235	Brady 360 Basic + MarkWare Standard	\$795.00
104237	Brady 360 Preferred + MarkWare Standard	\$995.00
104255	MiniMark Printer + Brady 360 Basic + MarkWare Standard	\$1990.00
104256	MiniMark Printer + Brady 360 Basic + MarkWare Lean	\$1990.00
104257	MiniMark Printer + Brady 360 Preferred + MarkWare Standard	\$2190.00
104258	MiniMark Printer + Brady 360 Preferred + MarkWare Lean	\$2190.00

The Next Small Thing in Fast Labeling



Labels



Pipe & Valve ID



General ID



Equipment ID



Bin & Shelf ID



Wire Markers

MiniMark™ Tapes & Ribbons

www.BradyID.com/minimark

Sign And Label Printers

Indoor/Outdoor Grade Vinyl Tape (B-595 Material)

- Ideal for Facility and Safety identification such as 5S labels, pipe markers, safety & warning labels, equipment & panel labels, arc flash labels, chemical labeling and more
- Conforms well to irregular, curved, rough and highly textured surfaces such as painted cinder block walls; finished uneven wood; textured plastics; rough-pipes; paper-jacketed pipes; and powder-coated surfaces.
- Adhere to "difficult" low-surface energy items including PVC piping, blow-molded equipment cases, ABS plastics, and equipment made from recycled plastics
- Low-shrink vinyl minimizes the amount of unsightly dust and grime buildup that is often found around the edges of other vinyl labeling supplies and also reduces adhesive buildup in label printer mechanisms.
- 8-10 year average outdoor durability in temperatures from -40°F to 180°F (-40°C to 82°C)
- Labels can be applied in temperatures from 0°F to 180°F
- Patent Number D481.414



Description	Catalog Number												Price
	White	Yellow	Red	Blue	Green	Black	Brown	Gold	Grey	Purple	Orange	Clear	
4"x100'	113182	113191	113196	113208	113204	113212	115759	115755	113218	113216	113200	113187	\$208.25
3"x100'	113183	113192	-	-	-	-	-	-	-	-	-	-	\$185.10
2.25"x100'	113184	113193	113197	113209	113205	113213	115760	115756	113219	113217	113201	113188	\$145.76
1.125"x100'	113185	113194	113198	113210	113206	113214	115761	115757	115753	115751	113202	113189	\$104.09
0.5"x100'	113186	113195	113199	113211	113207	113215	115762	115758	115754	115752	113203	113190	\$68.22



Ribbons For B-595 Vinyl

2 per pkg. 4" x 290'/roll

Description	Catalog #							Price
	White	Black	Red	Green	Yellow	Blue	Orange	
4" x 290'	103026	103025	103027	103029	103030	103028	103031	\$168.47

General Purpose Indoor/Outdoor Vinyl Tape (B-7569)

- Ideal for Facility and Safety identification such as 5S labels, pipe markers, safety & warning labels, equipment & panel labels, arc flash labels, chemical labeling and more
- Five year average outdoor durability in temperatures from -40°F to 180°F (-40°C to 82°C)
- Labels can be applied in temperatures from 0°F to 180°F
- Patent Number D481.414



Description	Catalog Number							Price
	White	Yellow	Red	Blue	Green	Black	Orange	
4" x 110'	120861	120862	120863	120865	120864	120867	120866	\$138.8
2.25" x 110'	120854	120855	120856	120858	120857	120860	120859	\$98.30
1.125" x 110'	120847	120848	120849	120851	120850	120853	120866	\$63.59



Ribbons for B-7569 General Purpose Vinyl

2 per pkg. 4.4" x 290'/roll

Description	Catalog #					Price
	White	Black	Red	Blue	Green	
4.4" x 290'	52044	52042	52045	52047	52059	\$110.05



Pre-Print Header Stripe Supply For Arc Flash Labels And Signs (B-595 Material)

- Pre-printed continuous stripe on top portion of white vinyl.
- Ideal for printing Arc Flash labels and other signs using Markware™ Software
- Use ribbons for B-595 Heavy Duty Vinyl


Description		Catalog #			Price
Tape Size	Stripe Width	Red Stripe	Orange Stripe	Yellow Stripe	
4" x 100'	1"	113221	113222	113220	\$219.27
3" x 100'	.75"	113225	113227	113226	\$196.12
2.25" x 100'	.50"	113230	113228	113229	\$156.78



Self Laminating Wire And Cable Markers (B-427 Self-Lam Vinyl)

Ideal for marking data cabling, this cable marker's protected printing offers superior abrasion resistance and resistance to dirt, oils, solvents and water. Marker features a clear, non-printed area which wraps around and overlaminates the printed text. Printer automatically "multiple repeats" your text in the white print area. B-427 Vinyl Self Laminating material.

- Resistant to abrasion, water, oil and solvents
- Temp range -94°F to 158°F (-70°C to 70°C)
- UL recognized




Part Number	# per Cartridge	Dimensions (in.)			Dimensions (mm)			Color	Price
		A	B	C	A	B	C		
52153	2,800/roll	0.50	1.25	0.50	12.7	31.8	12.7	BK on WT	\$98.30
52155	3,275/roll	1.00	1.00	0.375	25.4	25.4	9.5	BK on WT	\$173.52
52156	2,780/roll	1.00	1.25	0.50	25.4	31.8	12.7	Bk on WT	\$196.67
52157	1,485/roll	1.00	2.50	0.75	25.4	63.5	19.1	Bk on WT	\$196.67
52158	1,000/roll	1.50	2.50	0.75	38.1	63.5	19.1	Bk on WT	\$161.96

*Use Brady black ribbon Catalog # 105031 with die cut labels.



Tamper-Evident Metallized Polyester Labels (B-438 Material)

- Permanent adhesive
- Tape destructs into tiny fragments when tampered with, making removal very tedious and difficult

Description	Catalog No.	Label/Roll	Price Each
Silver  2" x 1"	52148	1,240/roll	\$124.66
3" x 1"	52149	1,225/roll	\$186.45
3" x 2"	52150	650/roll	\$186.45
3" x 110"	52152	Continuous	\$208.92

*Use Brady black ribbon Catalog # 105031 with die cut labels.

BBP[®]31 Sign & Label Printer

www.BradyID.com/bbp31

Sign And Label Printers



BBP[®]31 SIGN & LABEL PRINTER

Fast, Simple And Powerfully Versatile.
The way label making should be.

The BBP[®]31 Sign & Label Printer is exactly how a printer is supposed to be. It's easy to use. It's packed with functionality. And best of all, it's got so many material options that this one printer can handle all of the labeling needs in your facility.



Online Video:
www.BradyID.com/bbp31

Catalog #	Description	Price Each
BBP31	BBP31 Sign & Label Maker*	\$1,795.00
B31-WIPER	Extra BBP31 Media Wiper 5 Pack	\$22.95
B31-STYLUS	Extra BBP31 Replacement Stylus 3 Pack	\$12.95
B31-CCT	Extra BBP31 Cutter Cleaning Tool	\$12.95
B31-DC	BBP31 Dust Cover	\$12.95

*BBP31 Sign & Label Printer ships with printer, power cord, USB cable, drivers CD, stylus, cleaning kit, cutter cleaning tool, quick start guide and documentation holder.

U.S. Patent Nos. 5,318,370; 5,823,689; 6,570,602.
Additional Patents Pending.



- **Smart supplies.**

Drop in your material and ribbon cartridges, the printer does the rest. Smart cell technology tells the printer exactly how to format your label according to the material that's inserted.

- **Touch and go display.**

All the features you use most, right at your fingertips. This touch screen display lets you drag and drop objects and text until your label looks exactly the way you want it.

- **Applications abound.**

This one printer can take on all the different labeling needs of your facility. There are so many options packed into this printer, your applications are endless.

- **Stand alone or PC operation.**

You decide how you'd like to use the printer – either connected to your PC, or as a stand alone, mobile unit.

- **Powerful software options.**

MarkWare™ Software offers the industry's most advanced PC design and editing capabilities. There's more fonts, graphics, templates and import tools – and that's just the beginning.

- **Hundreds of material options.**

The BBP[®]31 Sign & Label Printer can print on continuous supplies, pre-cut labels and even pre-printed sign headers and chemical labels. Choose from hundreds of parts across 12 heavy-duty materials.

BBP[®]31 Sign & Label Printer

www.BradyID.com/bbp31

Seriously Simple Operation.

This printer is so simple, your whole team can use it. Just type and print – it's really that easy.


- Large touch-screen display with “touch and drag” moving and sizing
- 2-touch printing – just walk up and print!
- Drop, lock and print smart chip supplies for automatic label formatting
- Full size fold-down keyboard
- Stand alone or PC-connect operation



Chock-full Of Capabilities.

This one printer can take on all the different labeling needs of your facility.

- Prints labels from 1/2” to 4” wide
- 192 built-in graphics, with quick import options for graphics and fonts
- Wizard-style apps for pipe ID, arc flash, and RTK chemical labels
- Templates for common label styles such as signs with headers and a library of 266 pre-made “pick and print” signs and labels



Brady 360[®] Printer Protection & Care Plan

Brady 360 plans provide a printer extended warranty, loaner printer, free firmware upgrades and preventive care needed to extend the life of your BBP[®]31 Sign & Label Printer. Sold together with the printer or as a stand-alone plan (purchase of stand-alone plan allowed within 1 month after printer purchase).

Brady 360 Basic Plan – 3 years total warranty coverage and access to a loaner printer if your covered printer is in for service

Brady 360 Preferred Plan – same 3 yrs of warranty and loaner printer, plus one free *Brady 360[®] Preventive Maintenance Service*, free printer upgrades and two hours of *Brady 360[®] Professional Tech Support Services*.

For additional information & details visit www.BradyID.com/brady360

Catalog #	Description	Price Each
BBP31-360B	BBP31 Printer w/Brady 360 [®] Basic plan	\$2,145.00
BBP31-360P	BBP31 Printer w/Brady 360 [®] Preferred plan	\$2,395.00

*BBP31 Sign & Label Printer ships with printer, power cord, USB cable, drivers CD, stylus, cleaning kit, cutter cleaning tool, quick start guide and documentation holder.

** **Current MarkWare owners:** Markware v3.8.1 or higher required for use with BBP31, and MarkWare v3.7 required to upgrade to v3.8.1. both upgrades are free and available at www.BradyID.com.

BBP[®]31 PowerValue Packages and Printer Starter Packs

Save when you purchase our two most common accessories with your BBP[®]31 Sign & Label Printer. Powerful and easy-to-use MarkWare[™] Software takes your BBP31 label-making muscle to even higher levels. Add to that the protection of a Brady 360 Basic plan and you'll have the piece of mind knowing that your BBP[®]31 Sign & Label Printer will be ready to work for you whenever you need it



PowerValue Packages

Catalog #	Description	Price Each
BBP31-360B-MWS	BBP31 Printer w/Brady 360 [®] Basic Plan and MarkWare [™] Std Software	\$2,590.00
BBP31-360P-MWS	BBP31 Printer w/Brady 360 [®] Preferred Plan and MarkWare [™] Std Software	\$2,790.00

Printer + Tape Starter Packs (supply kit contents shown on page 138)

Catalog #	Description	Price Each
BBP31-ARCFLASH KIT	BBP31 Printer w/ Arc Flash Supply Kit	\$2,765.00
BBP31-SFTY KIT	BBP31 Printer w/ Safety & Compliance Supply Kit	\$3,140.00
BBP31-LEANVW KIT	BBP31 Printer w/ 5S Lean Visual Workplace Supply Kit	\$3,290.00
BBP31-PIPE KIT	BBP31 Printer w/ Pipe ID Supply Kit	\$3,720.00
BBP31-GENIND KIT	BBP31 Printer w/ General Industrial 5S Supply Kit	\$3,545.00

*BBP31 Sign & Label Printer ships with printer, power cord, USB cable, drivers CD, stylus, cleaning kit, cutter cleaning tool, quick start guide and documentation holder.

Just Walk Up and Print. So simple, your whole team can use it.



Industrial Labeling



Right To Know Labeling



Safety Tags



Visual Workplace Labeling



Raised Profile Labels



Safety Labels

...and many more.

BBP®31 Printer Materials

www.BradyID.com/bbp31

Sign And Label Printers

Indoor/Outdoor Vinyl (B-595)

For general facility and safety identification:
Our best industrial vinyl yet.

- Durable, low-shrink vinyl with our most aggressive adhesive
- Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper-jacketed pipes, powder-coated surfaces)
- Adheres to "difficult" low-surface energy items (PVC piping, blow-molded equipment cases, ABS plastics, recycled plastics)

Service temp: -40°F to 180°F Application temp: 0°F to 180°F

Average Outdoor Durability: 8-10 year outdoor vinyl label durability. Ribbon durability may vary.



NOTE: Use B30-R10000 black or colored ribbons. See page 140 for all BBP31 Ribbon part numbers.

		4"x100' \$221.98	3"x100' \$197.31	Catalog Number 2.25"x100' \$147.97	1.125"x100' \$98.63	0.5"x100' \$61.60
White		B30C-4000-595-WT	B30C-3000-595-WT	B30C-2250-595-WT	B30C-1125-595-WT	B30C-500-595-WT
Yellow		B30C-4000-595-YL	B30C-3000-595-YL	B30C-2250-595-YL	B30C-1125-595-YL	B30C-500-595-YL
Red		B30C-4000-595-RD	-	B30C-2250-595-RD	B30C-1125-595-RD	B30C-500-595-RD
Blue		B30C-4000-595-BL	-	B30C-2250-595-BL	B30C-1125-595-BL	B30C-500-595-BL
Green		B30C-4000-595-GN	-	B30C-2250-595-GN	B30C-1125-595-GN	B30C-500-595-GN
Orange		B30C-4000-595-OR	-	B30C-2250-595-OR	B30C-1125-595-OR	B30C-500-595-OR
Black		B30C-4000-595-BK	-	B30C-2250-595-BK	B30C-1125-595-BK	B30C-500-595-BK
Brown		B30C-4000-595-BR	-	B30C-2250-595-BR	B30C-1125-595-BR	B30C-500-595-BR
Gold		B30C-4000-595-GD	-	B30C-2250-595-GD	B30C-1125-595-GD	B30C-500-595-GD
Gray		B30C-4000-595-GY	-	B30C-2250-595-GY	B30C-1125-595-GY	B30C-500-595-GY
Purple		B30C-4000-595-PL	-	B30C-2250-595-PL	B30C-1125-595-PL	B30C-500-595-PL
Clear		B30C-4000-595-CL	-	B30C-2250-595-CL	B30C-1125-595-CL	B30C-500-595-CL

Low-Halide Polyester (B-569)

For labeling stainless steel and smooth surfaces.

- Low-halide content for labeling stainless steel pipes and surfaces
- Applies best to very smooth surfaces and ideal for mounting to rigid panels

Service temp: -40°F to 212°F Application temp: 0°F to 212°F Ave

Outdoor Durability: 3-5 years



NOTE: Use B30-R10000 black or colored ribbons. See page 140 for all BBP31 Ribbon part numbers.

		4"x100' \$232.07	3"x100' \$207.64	Catalog Number 2.25"x100' \$158.77	1.125"x100' \$109.90	0.5"x100' \$73.25
Clear		B30C-4000-569-CL	-	B30C-2250-569-CL	B30C-1125-569-CL	B30C-500-569-CL
White		B30C-4000-569-WT	B30C-3000-569-WT	B30C-2250-569-WT	B30C-1125-569-WT	B30C-500-569-WT
Yellow		B30C-4000-569-YL	-	B30C-2250-569-YL	B30C-1125-569-YL	B30C-500-569-YL
Red		B30C-4000-569-RD	-	B30C-2250-569-RD	B30C-1125-569-RD	B30C-500-569-RD
Blue		B30C-4000-569-BL	-	B30C-2250-569-BL	B30C-1125-569-BL	B30C-500-569-BL
Light Blue		B30C-4000-569-LB	-	B30C-2250-569-LB	B30C-1125-569-LB	B30C-500-569-LB
Sky Blue		B30C-4000-569-SB	-	B30C-2250-569-SB	B30C-1125-569-SB	B30C-500-569-SB
Green		B30C-4000-569-GN	-	B30C-2250-569-GN	B30C-1125-569-GN	B30C-500-569-GN
Orange		B30C-4000-569-OR	-	B30C-2250-569-OR	B30C-1125-569-OR	B30C-500-569-OR
Black		B30C-4000-569-BK	-	B30C-2250-569-BK	B30C-1125-569-BK	B30C-500-569-BK
Brown		B30C-4000-569-BR	-	B30C-2250-569-BR	B30C-1125-569-BR	B30C-500-569-BR
Ochre		B30C-4000-569-OC	-	B30C-2250-569-OC	B30C-1125-569-OC	B30C-500-569-OC
Tan		B30C-4000-569-TN	-	B30C-2250-569-TN	B30C-1125-569-TN	B30C-500-569-TN
Gray		B30C-4000-569-GY	-	B30C-2250-569-GY	B30C-1125-569-GY	B30C-500-569-GY
Purple		B30C-4000-569-PL	-	B30C-2250-569-PL	B30C-1125-569-PL	B30C-500-569-PL
Pink		B30C-4000-569-PK	-	B30C-2250-569-PK	B30C-1125-569-PK	B30C-500-569-PK

U.S. Patent Nos. 5,318,370; 5,823,689; 6,570,602.
Additional Patents Pending.

Pre-Printed Pre-Cut Blank Sign Headers (B-595)

- Allows printer to create multicolor signs fast - in a single print pass
- Headers meet OSHA 1910.145 and ASME/ANSI Z535 standards
- Indoor/outdoor grade material conforms to rough, irregular and "difficult to adhere to" surfaces

Service temp: -40°F to 180°F Application temp: 0°F to 180°F Average Outdoor Durability: 8-10 years



Did You Know?

Use these supplies with templates in the BBP®31 printer and MarkWare™ Software for arc flash labels and safety warning labels.



NOTE: Use B30-R10000 black or colored ribbons. See page 140 for all BBP31 Ribbon part numbers.

Legend	Catalog Number			
	4"x6" (175 labels/roll) \$221.98	2.25"x3" (300 labels/roll) \$147.97	2.25"x3.85" * (250 labels/roll) \$98.91	1.125"x2.85" * (300 labels/roll) \$98.91
	B30-25-595-ANSICA	B30-241-595-ANSICA	-	-
	B30-25-595-ANSIDA	B30-241-595-ANSIDA	-	-
	B30-25-595-ANSIWA	B30-241-595-ANSIWA	-	-
	B30-25-595-ANSINO	B30-241-595-ANSINO	-	-
	B30-25-595-OSHADA	B30-241-595-OSHADA	-	-
	B30-25-595-OSHACA	B30-241-595-OSHACA	-	-
	B30-25-595-BLNKWT	B30-241-595-BLNKWT	B30-219-595-BLNKWT	B30-242-595-BLNKWT
	B30-25-595-BLNKYL	B30-241-595-BLNKYL	-	-

*Pre-sized to fit blank rigid valve tags on page 136 but can also be used on its own as general purpose label.

Pre-Printed Right-To-Know Chemical Labels (B-595)

- Allows printer to produce 5-color chemical labels in a single print pass
- Indoor/outdoor grade material withstands exposure to moisture, chemicals and handling

Service temp: -40°F to 180°F Application temp: 0°F to 180°F Average Outdoor Durability: 8 to 10 years



Did You Know?

Use templates in the BBP®31 printer and MarkWare™ Software to enter your own chemical data or choose a pre-populated label from MarkWare's 2,000-chemical database.



NOTE: Use black ribbon B30-R10000 with these part numbers. See page 140 for all BBP31 Ribbon part numbers.

Size w/Text Area	NFPA Diamond w/Text Area	NFPA Diamond Only	NFPA Diamond NFR Label	Color Bar w/Text Area	Color Bar Only	Color Bar HMIG Format	Price Each
4"x6.25" (170/roll)	B30-243-595-NFPA	-	-	B30-243-595-CB	-	-	\$232.07
2.25"x4" (240/roll)	B30-245-595-NFPA	-	-	B30-245-595-CB	-	-	\$158.77
4"x4" (240/roll)	-	B30-161-595-NFPA	-	-	-	-	\$232.07
2.25"x2.25" (365/roll)	B30-244-595-NFPA	B30-244-595-DIAM	-	B30-244-595-CB	B30-244-595-HMIG	-	\$158.77
1.125"x3" (300/roll)	-	-	B30-246-595-NFR	-	-	B30-246-595-HMIG	\$109.90

BBP®31 Printer Materials

www.BradyID.com/bbp31

Sign And Label Printers

Non-Adhesive Pre-Printed & Pre-Cut Safety Tags (B-551)

Pre-printed and pre-cut to save you time!

- Non-adhesive semi rigid card stock
- Tags are pre-cut with hole and chamfered corners
- Perforated between tags
- Pre-printed with safety headers or blank white tag
- Snap-in plastic grommets available for extra strength around mounting hole

Service temp: -40°F to 180°F Application temp: 0°F to 180°F
Average Outdoor Durability: 8 to 10 years



NOTE: Use B30-R10000 black or colored ribbons.
See page 140 for all BBP31 Ribbon part numbers.

! Don't Forget Grommets

Plastic Snap-in Grommets are available to provide additional strength. (Catalog # 20596 - 100/Package)

3.25"x5.75" (100 tags/roll) \$169.88	3.25"x5.75" (100 tags/roll) \$169.88	3.25"x5.75" (100 tags/roll) \$169.88	3.25"x5.75" (100 tags/roll) \$169.88
B30-255-551-ANSIDA	B30-255-551-OSHADA	B30-255-551-ANSICA	B30C-255-551-WHT

Pre-Cut Blank Labels (B-595)

For general purpose, peel-off-and-apply identification.

- Ideal for a wide range of labeling applications
- 6 sizes available, 2 of which that are pre-cut and pre-sized to fit heavy-duty rigid tags
- Indoor/outdoor grade material
- Conforms well to rough, irregular and "difficult to adhere to" surfaces

Service temp: -40°F to 180°F Application temp: 0°F to 180°F
Average Outdoor Durability: 8 to 10 years



NOTE: Use B30-R10000 black or colored ribbons. See page 140 for all BBP31 Ribbon part numbers.

Color	4"x6" (175 labels/roll) \$221.98	2.25"x3" (300 labels/roll) \$142.89	2.25"x3.85" * (250 labels/roll) \$98.91	1.125"x2.85" * (300 labels/roll) \$98.91
White	B30-25-595-BLNKWT	B30-241-595-BLNKWT	B30-219-595-BLNKWT	B30-242-595-BLNKWT
Yellow	B30-25-595-BLNKYL	B30-241-595-BLNKYL	-	-

*Pre-sized to fit blank rigid valve tags below but can also be used on its own as general purpose label.

Make Your Own Heavy-Duty Rigid Tags

Heavy-duty valve tags and industrial tags.

- Use with Pre-Cut Blank Labels (B-595) from above (pre-cut to fit blank rigid tags)
- Tags have center hole for hanging; corner holes accept round wire or flat fastening straps
- Tag is non-conductive, non-corrosive; resistant to high-temps & impact
- Variety Pack combines 30 tags including at least one of each size and color. Perfect for evaluating which sizes and colors are needed for your application.



Color	Large 2.25"x4" \$2.36 (each)	Small 1.5"x3" \$2.18 (each)
Black Tag	41921	41920
Yellow Tag	41923	41922
Red Tag	41925	41924
Blue Tag	41927	41926
Green Tag	41929	41928
Orange Tag	87695	87694
White Tag	87697	87696
Gray Tag	87699	87698
Brown Tag	87711	87710
Tan Tag	87713	87712
Variety Pack	142133	

Tag Service temp: -40°F to 260°F


Non-Adhesive Continuous Tag Stock (B-551)

- Non-adhesive, semi rigid card stock
- Easy to hole-punch, staple or tack into place
- Great choice for Kanban cards and other lean and 5S card-in-pocket applications

Service temp: -40°F to 193°F Average Outdoor Durability: up to 2 years
Thickness: 0.35mm

NOTE: Use B30-R10000 black or colored ribbons.
See page 140 for all BBP31 Ribbon part numbers.



	4.25"x50'	3.25"x50'	2.5"x50'
Color	\$183.22	\$158.77	\$122.12
White 	B30C-4250-551-WT	B30C-3250-551-WT	B30C-2500-551-WT

Repositionable Vinyl (B-581)



For 5S and lean applications.

- Aggressive adhesive stays in place but removes cleanly without leaving adhesive residue
- Ideal for temporary, removable, and repositionable labels, like 5S and lean inventory labels

Service temp: -40°F to 180°F Application temp: 50°F to 180°F
Average Outdoor Durability: 5 years

NOTE: Use B30-R10000 black or colored ribbons.
See page 140 for all BBP31 Ribbon part numbers.



	4"x100'	2.25"x100'	1.125"x100'	0.5"x100'
Color	\$221.98	\$147.97	\$98.63	\$61.60
White 	B30C-4000-581-WT	B30C-2250-581-WT	B30C-1125-581-WT	B30C-500-581-WT
Yellow 	B30C-4000-581-YL	B30C-2250-581-YL	B30C-1125-581-YL	B30C-500-581-YL

Printable Magnetic Supply (B-509)



Easiest and quickest material for removing and repositioning.

- Non-adhesive magnetic material that can be printed on directly
- Ideal for reusable and repositionable identification applications

Service temp: 0°F to 158°F Average Outdoor Durability: 3 to 5 years

NOTE: Use B30-R10000 black or colored ribbons.
See page 140 for all BBP31 Ribbon part numbers.



	4.25"x25'	2.5"x25'
Color	\$122.12	\$91.57
White 	B30C-4250-509-WT	B30C-2500-509-WT
Yellow 	B30C-4250-509-YL	B30C-2500-509-YL

Cold Temperature Application Material (B-549)



For identification in temperatures as cold as -40°F.

- Special adhesive permanently adheres to extremely cold surfaces
- Can be applied in -10 °F and lasts in -40°F
- Ideal for cold storage warehouses, coolers, freezers, and short-term winter outdoor use

Service temp: -40°F to 212°F Application temp: -10°F to 212°F
Average Outdoor Durability: up to 1 year

NOTE: Use B30-R10000 black or colored ribbons.
See page 140 for all BBP31 Ribbon part numbers.



	4"x100'	2.25"x100'	1.125"x100'
Color	\$232.07	\$158.77	\$109.90
White 	B30C-4000-549-WT	B30C-2250-549-WT	B30C-1125-549-WT
Yellow 	B30C-4000-549-YL	B30C-2250-549-YL	B30C-1125-549-YL

BBP®31 Printer Materials

www.BradyID.com/bbp31

Sign And Label Printers

BradyGlo™ High-Intensity Photoluminescent Tape (B-526)


For glow-in-the-dark identification up to 10 hours!

- Designed for directional and evacuation marking
- Ideal for marking emergency utility shut-offs, fire extinguishers, alarm pulls, and vital equipment controls
- Complies with indoor use requirements specified in RS 6-1 and 6-1A of New York Local Law 26

Service temp: -40°F to 140°F Application temp: 40°F to 140°F

NOTE: Use B30-R10000 black or colored ribbons.
See page 140 for all BBP®31 Ribbon part numbers.



Color	2.25"x50'	1.125"x50'
Luminous Green 	\$226.95 B30C-2250-526	\$141.82 B30C-1125-526

Retro Reflective Tape (B-584)

For highly reflective identification that shines back brightly when struck by light.

- Ideal for labeling outdoor utility poles and pedestals, jobsite equipment and roof-top equipment
- Recommended low light or inclement weather conditions




Service temp: -40°F to 158°F

Application temp: 0°F to 158°F (yellow & orange), 50°F to 158°F (silver)

Average Outdoor Durability: 4 to 6 years

NOTE: Use B30-R10000 black or colored ribbons.
See page 140 for all BBP®31 Ribbon part numbers.




Color	4"x50'	2.25"x50'	1.125"x50'
Reflective Silver 	\$305.39 B30C-4000-584-SL	\$195.42 B30C-2250-584-SL	\$122.12 B30C-1125-584-SL
Reflective Yellow 	B30C-4000-584-YL	B30C-2250-584-YL	B30C-1125-584-YL
Reflective Orange 	B30C-4000-584-OR	B30C-2250-584-OR	B30C-1125-584-OR

Self-Laminating Cable & Wire Labels (B-427)

For wire and cable identification: Our most popular wire & cable labels.

- Conformable material designed to adhere to highly curved surfaces, wires and cables
- Features a white printable area with clear "tail" that wraps around marker
- Clear tail serves as over-laminate to protect the text, providing superior resistance to abrasion, dirt, oils, solvents, water and excessive handling

Service temp: -40°F to 158°F Application temp: 50°F to 158°F



NOTE: Use black ribbon B30-R6000 or white ribbon B30-R4400-WT with these part numbers. See page 140 for all BBP31 Ribbon part numbers.

Catalog Number	For Data Cables Sized To Fit	Wire Gauge	Labels Per Roll	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Price
B30-228-427	-	16-10 Gauge (.16" max dia)	4000	0.5" (12.7mm)	0.75" (19.05mm)	0.375" (9.525mm)	\$89.20
B30-229-427	-	16-10 Gauge (.16" max dia)	4000	1.00" (25.4mm)	0.75" (19.05mm)	0.375" (9.525mm)	\$89.20
B30-232-427	2 pair Fiber/Coaxial, Single/Multi Mode	12-10 Gauge (.21" max dia)	3000	0.50" (12.7mm)	1.00" (25.4mm)	0.375" (9.525mm)	\$89.20
B30-179-427	2 pair Fiber/Coaxial, Single/Multi Mode	12-10 Gauge (.21" max dia)	3300	1.00" (25.4mm)	1.00" (25.4mm)	0.375" (9.525mm)	\$157.45
B30-231-427	CAT-5, 4 pair UTP Copper	10-4 Gauge (.27" max dia)	2800	0.50" (12.7mm)	1.25" (31.75mm)	0.50" (12.7mm)	\$89.20
B30-227-427	CAT-5, 4 pair UTP Copper, Fiber, Coaxial	10-4 Gauge (.27" max dia)	2750	1.00" (25.4mm)	1.25" (31.75mm)	0.50" (12.7mm)	\$178.45
B30-225-427	CAT-5, 4 pair UTP Copper	10-4 Gauge (.27" max dia)	1800	1.50" (38.1mm)	1.25" (31.75mm)	0.50" (12.7mm)	\$146.95
B30-233-427	CAT-5, 4 pair UTP Copper, Fiber, Coaxial	10-4 Gauge (.32" max dia)	2300	1.00" (25.4mm)	1.50" (38.1mm)	0.50" (12.7mm)	\$178.45
B30-234-427	CAT-5, 4 pair UTP Copper, Fiber, Coaxial	10-4 Gauge (.32" max dia)	1500	1.50" (38.1mm)	1.50" (38.1mm)	0.50" (12.7mm)	\$146.95
B30-223-427	25 pair Copper, 4-12 pair Fiber, Coaxial	3 Gauge-2/0 (.53" max dia)	1500	1.00" (25.4mm)	2.50" (63.5mm)	0.75" (19.05mm)	\$178.45
B30-224-427	25 pair Copper, 4-12 pair Fiber, Coaxial	3 Gauge-2/0 (.53" max dia)	1000	1.50" (38.1mm)	2.50" (63.5mm)	0.75" (19.05mm)	\$146.95
B30-188-427	50 pair Copper, 24 pair Fiber, Backbone	3/0-400 kcmil (.85" max dia)	600	1.50" (38.1mm)	4.00" (101.6mm)	1.0" (25.4mm)	\$146.95
B30-226-427	100 pair Copper, 36 pair Fiber, Backbone	3/0-400 kcmil (1.3" max dia)	400	1.50" (38.1mm)	6.00" (152.4mm)	1.50" (38.1mm)	\$146.95

Raised Profile Labels - Engraved Plate Substitutes (B-593)

Costs up to 80% less than engraved legend plates.

- High gloss, polyester label with thick raised profile and ultra-aggressive adhesive. 0.70mm thick
- High performance, low cost substitute to engraved plates
- 10-year outdoor durability rating
- On-demand labeling: labels print out in less than 4 seconds
- Flexible labeling options: 6 colors, 7 rectangular sizes, 5 pushbutton sizes (including keyed and non-keyed 22.5mm and 30.5mm hole dia keyed)

Service temp: -4°F to 212°F Application temp: 50°F to 212°F
Average Outdoor Durability: Up to 10 years




! Cost Savings Example:

A 1" x 2" rectangular raised profile label costs approximately \$0.60, lasts up to 10 years outdoors and prints in seconds! A 22.5mm pushbutton label will cost you about \$0.32!



Push Button Style




NOTE: Use black ribbon B30-R6000 or white ribbon B30-R4400-WT with these part numbers. See page 140 for all BBP31 Ribbon part numbers.

Color		1.9"x1.2" 22.5mm dia keyed hole (180 labels/roll) \$129.92	1.5"x1.2" 22.5mm dia keyed hole (200 labels/roll) \$143.02	Catalog Number 1.5"x1.2" 22.5mm dia no key hole (200 labels/roll) \$143.02	1.8"x1.8" 30.5mm dia keyed hole (190 labels/roll) \$140.91	2.4"x2.4" 30.5mm dia keyed hole (145 labels/roll) \$135.11
White		B30EP-168-593-WT	B30EP-167-593-WT	B30EP-167U-593-WT	B30EP-169-593-WT	B30EP-170-593-WT
Black		B30EP-168-593-BK	B30EP-167-593-BK	B30EP-167U-593-BK	B30EP-169-593-BK	B30EP-170-593-BK
Red		B30EP-168-593-RD	B30EP-167-593-RD	B30EP-167U-593-RD	B30EP-169-593-RD	B30EP-170-593-RD
Green		B30EP-168-593-GN	B30EP-167-593-GN	B30EP-167U-593-GN	B30EP-169-593-GN	B30EP-170-593-GN
Yellow		B30EP-168-593-YL	B30EP-167-593-YL	B30EP-167U-593-YL	B30EP-169-593-YL	B30EP-170-593-YL

Corrected quantities shown, November 2011.

Rectangular Style



NOTE: Use black ribbon B30-R6000 or white ribbon B30-R4400-WT with these part numbers. See page 140 for all BBP31 Ribbon part numbers.

Color		2.5"x3" (125 labels/roll) \$159.27	1"x4" (300 labels/roll) \$233.37	1"x3" (300 labels/roll) \$233.37	Catalog Number 0.75"x3" (375 labels/roll) \$267.49	1"x2" (300 labels/roll) \$113.00	0.59"x1.77" (450 labels/roll) \$171.17	0.49"x1.06" (500 labels/roll) \$170.60
White		B30EP-177-593-WT	B30EP-174-593-WT	B30EP-176-593-WT	B30EP-175-593-WT	B30EP-173-593-WT	B30EP-172-593-WT	B30EP-171-593-WT
Black		B30EP-177-593-BK	B30EP-174-593-BK	B30EP-176-593-BK	B30EP-175-593-BK	B30EP-173-593-BK	B30EP-172-593-BK	B30EP-171-593-BK
Silver		-	B30EP-174-593-SL	-	-	B30EP-173-593-SL	B30EP-172-593-SL	B30EP-171-593-SL
Red		-	B30EP-174-593-RD	-	-	B30EP-173-593-RD	B30EP-172-593-RD	B30EP-171-593-RD
Green		B30EP-177-593-GN	B30EP-174-593-GN	B30EP-176-593-GN	B30EP-175-593-GN	B30EP-173-593-GN	B30EP-172-593-GN	B30EP-171-593-GN
Yellow		B30EP-177-593-YL	B30EP-174-593-YL	B30EP-176-593-YL	B30EP-175-593-YL	B30EP-173-593-YL	B30EP-172-593-YL	B30EP-171-593-YL

Corrected quantities shown, November 2011.

BBP®31 Print Ribbons

www.BradyID.com/bbp31

Sign And Label Printers

Tamper Evident Metallized Polyester Tape (B-438) and High Temp Metallized Polyester Tape (B-565)

For secure identification that indicates if it has been tampered with.

- B-438 tape leaves a “checkerboard” footprint if removed and a checkerboard also appears on top surface of label to prevent label re-use
- B-565 material has a high upper temperature rating and is not tamper evident
- Ideal for product rating plates, product warranty labels and asset identification labels

B-438: Service temp: -40°F to 104°F Application temp: 50°F to 104°F
 B-565: Service temp: -40°F to 230°F Application temp: 0°F to 230°F



NOTE: Use black ribbon B30-R4300 with these part numbers. See page 140 for all BBP31 Ribbon part numbers.

B-438 Tamper Evident Metallized Polyester	1"x2" (1,225 labels/roll)	1"x3" (1,225 labels/roll)	2"x3" (650 labels/roll)	3"x100 ft (continuous roll)
Silver Metallized	\$116.50	\$174.25	\$174.25	\$195.25
	B30-17-438	B30-18-438	B30-222-438	B30C-3000-438-SL

B-565 Metallized Polyester	4"x100'	2.25"x100'	1.125"x100'
Silver Metallized	\$305.39	\$195.42	\$122.12
	B30C-4000-565-SL	B30C-2250-565-SL	B30C-1125-565-SL



BBP®31 Print Ribbons

“Drop & Click” print ribbons for quick and easy supply changes.

- Tough, smear-proof ribbons that produce long-lasting printed text
- Print can withstand years in industrial areas and outdoor conditions
- Ribbons ship in self-contained cartridges that drop straight into printer with a “click”
- No calibrating, no threading, no waste, no hassles

BBP®31 Print Ribbons

Color	Catalog Number	Price
Black	B30-R10000	\$103.79
Black*	B30-R4300*	\$103.79
Black*	B30-R6000**	\$103.79
White	B30-R10000-WT	\$103.79
White*	B30-R4400-WT***	\$103.79
Red	B30-R10000-RD	\$103.79
Green	B30-R10000-GN	\$103.79
Blue	B30-R10000-BL	\$103.79
Yellow	B30-R10000-YL	\$103.79
Orange	B30-R10000-OR	\$103.79
Magenta	B30-R10000-MA	\$103.79

Use standard B30-R10000 series ribbon black, white and colored ribbons on all materials unless otherwise noted.

* NOTE: *B30-R4300 black ribbon for use with B-427 and B-438 materials only.


**B30-R6000 black ribbon for use with B-593 material only.

***B30-R4400-WT white ribbon for use with B-593 material only.

Tape Starter Packs

Everything you need to start your labeling applications.

These kits offer a variety of the most common labels to get you up and running quickly and easily! Tape Starter Packs are also available packaged with the BBP®31 Label Printer on page 132.



Arc Flash Warning Supply Kit (Available November 2011)

Catalog Number - B30KIT-ARCFLASH-W Price \$970.00

Contents:

- (2) 4" X 6" B595 ANSI WARNING HDR
- (1) 2" X 3" B595 ANSI WARNING HDR
- (3) BLACK RIBBON (B30-R10000)
- (1) 1" X 4" B593 WHITE
- (1) 2.2" B595 ORANGE



Safety & Compliance Supply Kit

Catalog Number - B30KIT-SFTY Price \$1,345.00

Contents:

- (1) 4" X 6" B595 ANSI DANGER HDR
- (1) 4" X 6" B595 ANSI WARNING HDR
- (1) 4" X 6" B595 ANSI CAUTION HDR
- (1) 4" X 6" B595 ANSI NOTICE HDR
- (2) BLACK RIBBON (B30-R10000)
- (1) RED RIBBON
- (1) 4" PHOS B526
- (1) 4" X 6" RTK NFPA DIA W/ TEXT



5S Visual Workplace Supply Kit

Catalog Number - B30KIT-LEANVW Price \$1,495.00

Contents:

- (1) 4" B595 WHITE
- (1) 2.2" B595 WHITE
- (1) 4" B595 YELLOW
- (1) 2.2" B595 YELLOW
- (1) 2.2" REPOS WHITE
- (1) 1.1" REPOS WHITE
- (1) 2.2" MAGNETIC WHITE
- (1) BLANK VALVE TAGS - VARIETY PACK - LG
- (1) LG DIE CUT LBLs FOR VALVE TAGS
- (1) 4" X 6" B595 CAUTION HDR
- (2) BLACK RIBBON (B30-R10000)
- (1) RED RIBBON
- (1) GREEN RIBBON
- (1) BLUE RIBBON



Pipe ID Supply Kit (Available November 2011)

Catalog Number - B30KIT-PIPE Price \$1,770.00

Contents:

- (1) 4" B595 YELLOW
- (1) 2.2" B595 YELLOW
- (1) 1.1" B595 YELLOW
- (1) 4" B595 GREEN
- (1) 2.2" B595 GREEN
- (1) 1.1" B595 GREEN
- (1) 1.1" B595 BLUE
- (1) 2.2" B595 RED
- (1) 1.1" B595 RED
- (1) 1" X 4" B593 BLACK
- (1) BLANK VALVE TAGS - VARIETY PACK - SM
- (1) SM DIE CUT LBLs FOR VALVE TAGS
- (3) BLACK RIBBON (B30-R10000)
- (2) WHITE RIBBON



General Industrial & 5S Supply Kit (Available November 2011)

Catalog Number - B30KIT-GENIND Price \$1,750.00

Contents:

- (1) 4" B595 WHITE
- (1) 2.2" B595 WHITE
- (1) 1.1" B595 WHITE
- (1) 4" B595 YELLOW
- (1) 2.2" B595 YELLOW
- (1) 1.1" B595 YELLOW
- (1) 2.5" X 3" B593 WHITE ON BLACK
- (1) 4" X 6" B595 DANGER HDR
- (1) 4" X 6" B595 CAUTION HDR
- (1) 2" REFL YELLOW
- (1) 4" TAG STOCK WHITE
- (2) BLACK RIBBON (B30-R10000)
- (1) WHITE RIBBON
- (1) RED RIBBON

GlobalMark®2 Industrial Label Maker

www.BradyID.com/globalmark

GLOBALMARK®2 INDUSTRIAL LABEL MAKER

Sign And Label Printers

- Multicolor spot printing or Full-color process printing
- Cuts characters & shapes!
- Color touch screen interface... Quick & Easy!
- New materials including tag stock, magnetic and static cling!
- Patent # D481,415

Brady File Management Utility allows you to:

- Transfer files from your PC to your GlobalMark and from your GlobalMark to your PC
- Manage your existing GlobalMark files
- Update your GlobalMark operating system when upgrades are available.
- Simple to run when connected to your PC

Catalog No.	Description	Price Each
76801	GlobalMark® Color & Cut	\$4,495.00
76800	GlobalMark® MultiColor	\$3,495.00

All models include Printer, Keyboard & USB cable.
See additional GlobalMark® printer packages on facing page.

Accessories for GlobalMark®

Catalog #	Description	Price Each
76802	Hard Carrying Case w/Wheels	\$297.62
76808	Mouse	\$18.79
76809	Stylus Pens (3 pack)	\$37.64
76810	Compact Flash	\$49.29
76811	Replacement Cutting Blade	\$37.64

Multi-Color Printing

Quickly and easily print multi-color labels like this with the GlobalMark®2 Label Maker!



GlobalMark[®] 2 Industrial Label Maker

www.BradyID.com/globalmark

Choose from 2 GlobalMark[®] Models that meet all your labeling requirements

COLOR & CUT Catalog No. 76801

- Prints in one color, multiple spot colors, blended colors and full process color
- Unit has an additional built-in plotter cutter for cutting out characters, text, shapes and multi-up labels.
- With optional MarkWare[™] label making software, import and print full color logos, artwork, even photographs



MULTI COLOR - Catalog No. 76800

- Prints the same color options as the Color & Cut system, including the optional MarkWare[™] software enhancements, without the additional built-in plotter cutter

Brady 360[®] Printer Protection & Care Plan

Brady 360 plans provide a printer extended warranty, loaner printer, free firmware upgrades and preventive care needed to extend the life of your Globalmark printer. Sold together with the printer or as a stand-alone plan (purchase of stand-alone plan allowed within 1 month after printer purchase).

Brady 360 Basic Plan – 3 years total warranty coverage and access to a loaner printer if your covered printer is in for service

Brady 360 Preferred Plan – same 3 yrs of warranty and loaner printer, plus one free Brady 360[®] Preventive Maintenance Service, free printer upgrades and two hours of Brady 360[®] Professional Tech Support Services.

For additional information & details visit www.bradyid.com/brady360

Catalog No.	Description	Price Each
114447	Brady 360 Basic - For Desktop Facility ID Printer	\$350.00
114448	Brady 360 Preferred - For Desktop Facility ID Printer	\$600.00
114450	GlobalMark2 Multicolor Printer with Brady 360 Basic	\$3845.00
114455	GlobalMark2 Multicolor Printer with Brady 360 Preferred	\$4095.00
114451	GlobalMark2 Color & Cut Printer with Brady 360 Basic	\$4845.00
114456	GlobalMark2 Color & Cut Printer with Brady 360 Preferred	\$5095.00

GlobalMark[®] PowerValue Packages

Save when you purchase our two most common accessories with your Globalmark printer. Powerful and easy-to-use MarkWare[™] Software takes your Globalmark label-making muscle to even higher levels. Add to that the protection of a Brady 360 Basic plan and you'll have the piece of mind knowing that your GlobalMark will be ready to work for you whenever you need it.

Catalog No.	Description	Price Each
104235	Brady 360 Basic + MarkWare Std	\$795.00
104236	Brady 360 Basic + MarkWare Lean	\$795.00
104237	Brady 360 Preferred + MarkWare Std	\$995.00
104238	Brady 360 Preferred + MarkWare Lean	\$995.00
104243	GlobalMark2 Multicolor printer + Brady 360 Basic + MarkWare Std	\$4,290.00
104244	GlobalMark2 Multicolor printer + Brady 360 Basic + MarkWare Lean	\$4,290.00
104245	GlobalMark2 Multicolor printer + Brady 360 Preferred + MarkWare Std	\$4,490.00
104246	GlobalMark2 Multicolor printer + Brady 360 Preferred + MarkWare Lean	\$4,490.00
99004	GlobalMark2 Multicolor printer + LockoutPRO software	\$4,150.00
104247	GlobalMark2 ColorCut printer + Brady 360 Basic + MarkWare Std	\$5,290.00
104248	GlobalMark2 ColorCut printer + Brady 360 Basic + MarkWare Lean	\$5,290.00
104249	GlobalMark2 ColorCut printer + Brady 360 Preferred + MarkWare Std	\$5,490.00
104250	GlobalMark2 ColorCut printer + Brady 360 Preferred + MarkWare Lean	\$5,490.00
99009	GlobalMark2 ColorCut printer + LockoutPRO software	\$5,150.00

Look what GlobalMark[®] can do for you...




Pipe Markers (1/2" to 4")



Valve tags




Equipment I.D.




Cut Shapes




RTK Chemical Labels



Panels/Motor Control




Cut Characters




Logo-Friendly



Process Color Printing



Print to Magnetic



Print to Tagstock

Wide Range of Industrial Strength Materials!

- Drop-n-lock to load tapes & ribbons...easy!
- Maximum durability...more than just office-grade material
- Many materials offer 5+ year outdoor durability



Brady outdoor grade tapes for the GlobalMark™ printer come in .5", 1.125", 2.25", 3" and 4" widths, 17 colors and 12 materials.



Indoor/Outdoor Grade Vinyl Tape (B-595 Material)

- Ideal for Facility and Safety identification such as 5S labels, pipe markers, safety & warning labels, equipment & panel labels, arc flash labels, chemical labeling and more
- Conforms well to irregular, curved, rough and highly textured surfaces such as painted cinder block walls; finished uneven wood; textured plastics; rough-pipes; paper-jacketed pipes; and powder-coated surfaces.
- Adheres to "difficult" low-surface energy items including PVC piping, blow-molded equipment cases, ABS plastics, and equipment made from recycled plastics
- Low-shrink vinyl minimizes the amount of unsightly dust and grime buildup that is often found around the edges of other vinyl labeling supplies and also reduces adhesive buildup in label printer mechanisms.
- 8-10 year average outdoor durability in temperatures from -40°F to 180°F (-40°C to 82°C)
- Labels can be applied in temperatures from 0F to 180°F
- Patent Number D481.414



Description	Catalog Number											Price	
	White	Yellow	Red	Blue	Green	Black	Brown	Gold	Grey	Purple	Orange		Clear
4"x100'	113109	113114	113119	113127	113123	113131	113135	113139	113143	113147	113151	113105	\$237.52
3"x100'	113110	113115	-	-	-	-	-	-	-	-	-	-	\$211.12
2.25"x100'	113111	113116	113120	113128	113124	113132	113136	113140	113144	113148	113152	113106	\$158.33
1.125"x100'	113112	113117	113121	113129	113125	113133	113137	113141	113145	113149	113153	113107	\$105.53
0.5"x100'	113113	113118	113122	113130	113126	113134	113138	113142	113146	113150	113154	113108	\$65.91

Polyester Tape (B-569 Material)

- Outdoor Grade
- Best choice for marking stainless steel pipes & surfaces (low halide content)
- Ultra-smooth finish excellent for mounting to rigid panels & very smooth surfaces.
- Applies best to very smooth surfaces

Description	Catalog Number					Price
	Pink	Tan	Lt. Blue	Ochre	Sky Blue	
4" x 100'	76598	76602	76606	97738	97742	\$255.76
3" x 100'	-	-	-	-	-	\$228.84
2.25" x 100'	76599	76603	76607	97739	97743	\$174.98
1.125" x 100'	76600	76604	76608	97740	97744	\$121.12
0.5" x 100'	76601	76605	76609	97741	97745	\$80.73

Description	Catalog Number											Price
	Clear	White	Yellow	Red	Blue	Purple	Orange	Green	Brown	Black	Grey	
4" x 100'	76610	76614	76619	76623	76627	76631	76635	76639	76643	76647	76651	\$255.76
3" x 100'	-	76615	-	-	-	-	-	-	-	-	-	\$228.84
2.25" x 100'	76611	76616	76620	76624	76628	76632	76636	76640	76644	76648	76652	\$174.28
1.125" x 100'	76612	76617	76621	76625	76629	76633	76637	76641	76645	76649	76653	\$121.12
0.5" x 100'	76613	76618	76622	76626	76630	76634	76638	76642	76646	76650	76654	\$80.73


ToughStripe® Print-On-Demand Floor Labels

- Create custom-printed floor labels using your GlobalMark™2 Label Maker!
- Revolutionary new B-514 material has ultra aggressive adhesive
- Withstands forklift and pallet jack traffic without tearing or lifting
- Easy 3-step process: print label, position on floor, apply overlamine
- Each roll ships with a roll of clear overlamine



Description	Catalog Number							Price Each
	White	Black	Yellow	Red	Blue	Green	Orange	
1.125" x 100'	142155	142159	142162	142166	142169	142172	142175	\$168.05
2.25" x 100'	142154	142158	142161	142165	142168	142171	142174	\$255.51
3" x 100'	142156	-	142163	-	-	-	-	\$321.35
4" x 100'	142157	142160	142164	142167	142170	142173	142176	\$358.16

View more ToughStripe Floor Marking products on pages 88-92.



Phosphorescent B-526 Tape

- Permanent adhesive
- Extended Illumination
- High-intensity glow
- Glows brighter and longer than B-582



Description	Catalog Number	Price Each
Size	Phosphorescent	
4" x 50'	105909	\$390.84
2½" x 50'	105910	\$250.13
1½" x 50'	105911	\$156.30

Phosphorescent B-582 Tape


- Permanent adhesive
- Glows in darkness for 10 hours
- Meets ISO, DIN & ASTM standards



Description	Catalog Number	Price Each
Size	Phosphorescent	
4" x 50'	76711	\$336.57
2½" x 50'	76712	\$215.37
1½" x 50'	76713	\$134.59

Reflective B-584 Tape

- Permanent adhesive/outdoor grade
- Shines back at viewer brightly when light shines on label
- Not recommended for plotter cutting



Description	Catalog Number				
Tape Cartridges	No. Per Pkg.	Silver	Yellow	Orange	Price Each
4" x 50'	1	76705	96060	99219	\$336.57
2¼" x 50'	1	76706	96061	99220	\$215.37
1½" x 50'	1	76707	96062	99221	\$134.59

Tag Stock B-551 Material

- Non-adhesive tag stock
- Grommets (Catalog # 20596, \$13.72)
- 5/8" Hole punch (Catalog # 20591, \$131.92)
- Meets OSHA 50 lb. pull requirement



Description	Catalog Number	
Size	White	Price Each
4¼" x 50'	76714	\$196.05
3¼" x 50'	76715	\$169.88
2½" x 50'	76716	\$130.67



Repositionable B-581 Vinyl Tape

- Special adhesive allows you to easily remove the label and re-apply again...and again
- Label of choice for indoor marking where frequent repositioning is required, such as storage shelves

Size	White	Yellow	Price Each
4" x 100'	76697	76701	\$235.24
2¼" x 100'	76698	76702	\$156.82
1½" x 100'	76699	76703	\$104.52
½" x 100'	76700	76704	\$65.29



Cold Temperature B-549 Tape

- Permanently adheres to surfaces at temperatures as low as -10°F
- Great for use in any cold storage warehouse, cooler or freezer
- Not recommended for plotter cutting

Size	White	Yellow	Price Each
4¼" x 100'	76691	76694	\$255.76
2½" x 100'	76692	76695	\$174.98
1½" x 100'	76693	76696	\$121.12



Magnetic B-509 Tape

- Non-adhesive
- Print direct to magnetic tape

Size	White	Yellow	Price Each
4¼" x 25'	76686	76688	\$130.67
2½" x 25'	76687	76689	\$97.98

Right-to-Know Pre-Print Labels for GlobalMark® Printer (B-595 Material)

- Outdoor grade vinyl adhesive
- Color Bar or NFPA 704M diamond formats
- 4 color diamond or bars are pre-printed so these only require 1-color print pass (black) through printer

! Special Black Ribbon Required

Pre-printed RTK Labels require the use of ribbon catalog number 96089.

Catalog #	Description	Price
96089	4.11" x 200' RTK Black Ribbon	\$111.06



Available in NFPA Diamond and Color Bar Format.



Alert employees of chemicals with Right-to-Know Labels.

Right-to-Know Labels

Size	NFPA Diamond w/Text Area	NFPA Diamond Diamond Only	Color Bar w/Text Area	Color Bar Color Bar Only	Color Bar HMIG Format	NFPA Diamond NFR Label	Price Per Cartridge
2½" x 4" (240/roll)	115766	-	115767	-	-	-	\$169.88
4" x 6½" (170/roll)	115763	-	115764	-	-	-	\$248.31
4" x 4" (240/roll)	-	115765	-	-	-	-	\$232.07
2¼" x 2½" (365/roll)	115772	115773	115771	115768	-	-	\$169.88
1½" x 3" (300/roll)	-	-	-	-	115770	115769	\$117.59

Hand-Applied Overlaminates for RTK Labels (B-674 Materials)

Protect your printed labels with a pressure sensitive polyester overlaminate.

Size	Quantity Per Pkg.	Catalog Number	Price Per Pkg.
1½" x 2½"	50	64984	\$ 5.04
2½" x 2½"	50	58476	\$ 9.26
3½" x 5½"	50	58706	\$24.75
4½" x 6½"	50	64985	\$33.72

! Software Solutions

MarkWare™ Facility Identification Software allows you to create custom Hazchem labels or instantly auto-populate your label with data from a 2,200-chemical database. See page 156 for more information.

Metalized B-565 Polyester Tape

- Permanent adhesive
- Great choice for multicolor OEM labels, rating plates, etc.
- Non-cuttable supply suitable for continuous-style labels
- Cuttable supply ideal for multi-up, cut labels in basic rectangular & round shapes only. Not suitable for cut-out text or intricate shapes.



Description	Catalog Number		Price
	Non-cuttable Metallized	Cuttable Metallized	
Size			
4.25" x 100'	76720	114533	\$336.57
2.50" x 100'	76721	-	\$215.37
1.375" x 100'	76722	-	\$134.59

Transfer Tape For Cut Text

- Leaves cut characters pre-spaced for transferring from liner to applying them to desired surface

Size	Catalog Number	Price
4/4" x 200'	76737	\$65.29

Brushed Gold B-575 Material

Adhesive, but semirigid

Description	Catalog Number	Price
Size	Gold	
4" x 50'	76685	\$134.59

Pre-Printed Header Stripe Supply (B-595)

- Pre-printed continuous stripe on top portion of white industrial vinyl. Ideal for printing Arc Flash labels from Markware Deluxe Software



Description	Catalog Number				Price
		Red Stripe	Orange Stripe	Yellow Stripe	
Tape Size	Stripe Width				
4" x 100'	1"	113161	113162	113163	\$232.07
3" x 100'	.75"	113157	113158	113159	\$207.64
2.25" x 100'	.50"	113155	113156	115774	\$158.77

*Use black ribbon Catalog # 96089 with these supplies.

Industrial Grade Print Ribbons

- Super-Tough smear-proof ribbons assure your printed text lasts for years outdoors and in an industrial environment
- Ribbons ship self-contained in cartridges that drop straight in to the GlobalMark™ with a "click"
- 2 and 4-color "paneled" ribbons are used to print labels and signs containing more than 1 print color
- Patent D481, 755



Single Color Print Ribbon Cartridges – 200 ft./roll

Size	Catalog No.											Price
	Black	White	Red	Blue	Green	Magenta	Yellow	Orange	Process Cyan	Process Yellow	Process Magenta	
4.11" x 200 ft.	76739	76741	76743	76745	76747	76749	76751	76752	76759	76760	76761	\$111.06

Two Color Print Ribbon Cartridges – 200 ft./roll (Not available for MonoColor)

Size	Catalog No.							Price
	Black & Red	Red & Green	Black & Blue	Black & Yellow	Black & Orange	Black & Green	Red & Blue	
4.11" x 8" Panels	76763	110220	76775	76767	76771	76779	-	\$113.18
4.11" x 16" Panels	76762	-	76774	76766	76770	76778	76782	\$113.18

Typical yield from 2-color ribbons: 100-8in labels from 8" paneled ribbon; 60-16in labels from 16" paneled ribbon

Four Color Print Ribbon Cartridges – 200 ft./roll (Not available for MonoColor)

Size	Catalog No.					Price
	Blk/Red/Blue/Green	Red/Green/Yellow/Blk	Blk/Red/Blue/Yellow	Cyan/Magenta/Yellow/Blk	Blk/Red/Orange/Blue	
4.11" x 8" Panels	76787	110221	76791	76795	51447	\$115.34
4.11" x 16" Panels	76786	N/A	76790	76794	N/A	\$115.34

Typical yield from 4-color ribbons: 50-8in labels from 8" paneled ribbon; 60-16in labels from 16" paneled ribbon

PowerMark® Sign & Label Maker

www.BradyID.com/powermark

BRADY

POWERMark

sign and label maker

Sign And Label Printers

Make Your Labels & Signs Stand Out in the Crowd!

- Multiple color printing and 10" wide output... get noticed!
- Industrial strength, outdoor grade tapes and ribbons
- Patent # 6,276,849

Description	Catalog No.	Price Each
PowerMark® Sign and Label Maker* Includes: Printer & keyboard & parallel cable & USB cable	13500	\$4,995.00

10" WIDE OUTPUT

Applies multiple print colors with no user intervention

On-screen preview

Type sizes 1/16" to 7/2"

4", 6", 7", 8" and 10" tape widths

Large, pivoting screen

Internal and external file storage

Includes Full size QWERTY keyboard

Multi Color Printing

Over 300 built-in symbols

11 international operating languages

Built-in applications:

- Signs
- Hazardous waste labels
- Pipe markers
- Freeform custom label creation

3 bar code symbologies built-in!

- 3 of 9
- 128
- 2 of 5
- 13 more available if using MarkWare™ software

Text Options:

- Multiple color printing
- Bold, Underline, Italics, Reverse
- Expand/condense text
- Superscript/subscript
- Auto fit to specific length
- Frames automatically
- Justify text automatically
- Repeat printing, auto sequencing

Big...Bold...Colorful...Output Custom Signs and Labels on the Spot When You Need Them!

- Multiple colors increase the visual impact of your signs and labels
- Helps you meet labeling regulations
- Enhance productivity through improved visual communication where you need it, when you need it, in the size you need it
- Huge cost savings compared to custom ordering from shops
- When PC connected, MarkWare™ Software increases the range of available templates, fonts and bar codes including a 2000 chemical database for Right-To-Know labels



Produces multi-color output up to 10" wide.

Accessories for PowerMark® Sign and Label Maker

Description	Catalog Number	Price Each
Spare Ribbon Cassette (holds ribbon)	13507	\$40.13
PowerMark® Replacement Wiper Pads	13644	\$12.70
PowerMark® Carry Case	13700	\$334.90

Brady 360® Printer Protection & Care Plan

Brady 360 plans provide a printer extended warranty, loaner printer, free firmware upgrades and preventive care needed to extend the life of your PowerMark printer. Sold together with the printer or as a stand-alone plan (purchase of stand-alone plan allowed within 1 month after printer purchase)

Brady 360 Basic Plan – 3 years total warranty coverage and access to a loaner printer if your covered printer is in for service

Brady 360 Preferred Plan – same 3 yrs of warranty and loaner printer, plus one free *Brady 360® Preventive maintenance service*, free printer upgrades and two hours of *Brady 360® Professional Tech Support Services*.

For additional information & details visit www.bradyid.com/brady360

Catalog No.	Description	Price Each
114447	Brady 360 Basic - For Desktop ID Facility Printer	\$350.00
114448	Brady 360 Preferred - For Desktop ID Facility Printer	\$600.00
114452	PowerMark Printer with Brady 360 Basic	\$5,345.00
114457	PowerMark Printer with Brady 360 Preferred	\$5,595.00

PowerMark PowerValue Package

Save when you purchase our two most common accessories with your PowerMark printer. Powerful and easy-to-use MarkWare™ Software takes your powermark label-making muscle to even higher levels. Add to that the protection of a Brady 360 Basic plan and you'll have the piece of mind knowing that your PowerMark will be ready to work for you whenever you need it.

Catalog No.	Description	Price Each
104235	Brady 360 Basic + MarkWare Standard	\$795.00
104237	Brady 360 Preferred + MarkWare Standard	\$995.00
104251	PowerMark Printer + Brady 360 Basic + MarkWare Standard	\$5,790.00
104252	PowerMark Printer + Brady 360 Basic + MarkWare Lean	\$5,790.00
104253	PowerMark Printer + Brady 360 Preferred + MarkWare Standard	\$5,990.00
104254	PowerMark Printer + Brady 360 Preferred + MarkWare Lean	\$5,990.00
89244	PowerMark Printer + BLS1255 Laminator + Brady 360 Basic + MarkWare Standard	\$5,595.00

Custom Signs on the Spot When You Need Them



Larger Signs (up to 10")



Security Procedures



Emergency Evacuation Signs



Special Events



Hazard Notification




Roll Form Pipe Markers

Industrial Strength Output!

- PowerMark™ uses Brady's easy-to-load ribbons and high quality, industrial strength tapes
- Maximum durability...these are not office grade tapes
- Many materials offer 5+ years outdoor durability



Brady's Indoor/Outdoor tapes for the PowerMark™ come in 4", 6", 7", 8" and 10" widths and 15 colors.



Indoor/Outdoor Grade Vinyl Tape (B-595 Material)

- Ideal for Facility and Safety identification such as 5S labels, pipe markers, safety & warning labels, equipment & panel labels, arc flash labels, chemical labeling and more
- Conforms well to irregular, curved, rough and highly textured surfaces such as painted cinder block walls; finished uneven wood; textured plastics; rough-pipes; paper-jacketed pipes; and powder-coated surfaces.
- Adheres to "difficult" low-surface energy items including PVC piping, blow-molded equipment cases, ABS plastics, and equipment made from recycled plastics
- 8-10 year average outdoor durability in temperatures from -40°F to 180°F (-40°C to 82°C). Application temperature 0°F to 180°F

Size	Catalog Number												
													Price Each
Width	White	Yellow	Red	Blue	Green	Orange	Black	Gold	Grey	Brown	Purple	Clear	Price Each
4" x 50' (100mm x 15.2m)	13538	13539	13540	13541	13542	13543	13544	13545	13546	13547	13548	59529	\$148.21
6" x 50' (152mm x 15.2m)	13549	13550	13601	13602	13603	13604	13605	13606	13607	13608	13609	59530	\$177.86
7" x 50' (178mm x 15.2m)	13651	13652	13654	13656	13655	13653	—	—	—	—	—	—	\$207.51
8" x 50' (203mm x 15.2m)	13551	13552	13553	13554	13555	13556	13557	13558	13559	13560	13561	59531	\$222.32
10" x 50' (254mm x 15.2m)	13562	13563	13610	13611	13612	13613	13614	13615	13616	13617	13618	59532	\$266.82

Reflective B-584 Tape

- Suitable for indoor or outdoor use
- Reflective capabilities are ideal for reading labels in low light conditions with a flashlight or from a vehicle
- Applications include utility pole and box labeling, door labeling, labeling rooftop equipment and equipment that needs to be viewed from a road side



Description	Catalog Number			Price Each
Size	Silver	Orange	Yellow	Price Each
4" x 33' (100mm x 10m)	13580	13404	51584	\$198.47
7" x 33' (178mm x 10m)	13585	13403	51585	\$274.82
10" x 33' (254mm x 10m)	13590	13402	51586	\$366.46

Low-Halide Polyester B-569 Tape

- Ultra smooth outdoor grade tape
- Ideal for mounting on sign panels
- Low halide construction makes this the best choice for labeling stainless steel and nickel surfaces
- Applies best to very smooth surfaces



Size	Catalog Number					
						Price Each
Width	Clear	White	Yellow	Orange	Ochre	Price Each
4" x 50' (100mm x 15.2m)	13564	13565	13566	13567	99167	\$163.01
6" x 50' (152mm x 15.2m)	13568	13569	13570	13571	99168	\$200.09
7" x 50' (178mm x 15.2m)	13572	13573	13574	13575	99169	\$222.32
10" x 50' (254mm x 15.2m)	13576	13577	13578	13579	99170	\$296.48



May we also suggest BLS1255 Laminator for rigid signs. See page 158.

Glow-In-The-Dark Phosphorescent B-582 Tape

- Glows for 10 hours in darkness
- Meets ISO, DIN and ASTM standards



Description	Catalog Number	Price
Size	Phosphorescent	
4" x 33' (100mm x 10m)	13582	\$198.47
7" x 33' (178mm x 10m)	13587	\$274.82
10" x 33' (254mm x 10m)	13592	\$366.46

Tag Stock & Other Specialty Tapes

- Print directly to tag stock
- Grommets & hole punch for tag stock available
- Brushed gold is shiny and great for office environment



Description	Catalog Number	Price
Size	Tag Stock (B-551)	Brushed Gold (B-575)
4" x 33' (100mm x 10m)	13583	13584
7" x 33' (178mm x 10m)	13588	13589
10" x 33' (254mm x 10m)	13593	13594



Phosphorescent B-526 Tape

- Glows brighter and longer than B-582
- Permanent adhesive
- Extended Illumination
- High-intensity glow

Description	Catalog Number	Price
Size	Phosphorescent	
4" x 33'	105912	\$216.85
7" x 33'	105913	\$299.61
10" x 33'	105914	\$399.50



Industrial Grade Print Ribbons for PowerMark®

- Super-tough, smear-proof ribbons ensure your printed text lasts for years outdoors and in industrial areas
- 2 and 4-color "paneled" ribbons are used to print labels & signs with more than 1 print color

1 Color Ribbons

Size	Catalog Number								Price Each
Width	Black	White	Red	Blue	Green	Magenta	Yellow	Orange	
6.25" x 200' (158mm x 60.8m)	13511	13513	13595	13596	13597	13598	13599	13600	\$177.86
8.8" x 200' (224mm x 60.8m)	13510	13512	13514	13515	13516	13517	13518	13519	\$200.09

Spare ribbon cassette (holder)
Catalog # 13507, Price \$40.13



2 Color Paneled Ribbons - 8" long panels

Size	Catalog Number				Price Each
Width	Blk/Red	Blk/Green	Blk/Yellow	Blk/Orange	
6.25" x 200' (158mm x 60.8m)	13523	13704	13527	13529	\$207.51
8.8" x 200' (224mm x 60.8m)	13522	13706	—	—	\$229.74

(used to create 2 color signs up to 8"long)

2 Color Paneled Ribbons - 15" long panels

Size	Catalog Number					Price
Width	Blk/Red	Blk/Blue	Blk/Yellow	Blk/Orange	Blk/Green	
6.25" x 200' (158mm x 60.8m)	13521	13525	—	—	13705	\$207.51
8.8" x 200' (224mm x 60.8m)	13520	13524	13526	13528	13707	\$229.74

(used to create 2 color signs up to 15"long)

4 Color Paneled Ribbons - 8" long panels

Size	Catalog Number			Price
Width	Blk/Red/Blue/Yel.	Blk/Red/Blue/Grn.	Blk/Red/Org./Blue	
6.25" x 200' (158mm x 60.8m)	13533	13537	NA	\$266.82
8.8" x 200' (224mm x 60.8m)	13532	13536	51448	\$296.48

(used to create 4 color signs up to 8"long)

4 Color Paneled Ribbons - 15" long panels

Size	Catalog Number		Price
Width	Black/Red/Blue/Yellow	Black/Red/Blue/Green	
6.25" x 200' (158mm x 60.8m)	13531	13535	\$266.82
8.8" x 200' (224mm x 60.8m)	13530	13534	\$296.48

(used to create 4 color signs up to 15"long)

Labelizer® Plus & VersaPrinter™ Tapes

www.BradyID.com

Sign And Label Printers



Discontinued Printer Supplies Still Available!

Tapes for the Labelizer® PLUS and VersaPrinter™ machines are still manufactured and fully stocked...the full range is shown on the next 3 pages.



Indoor/Outdoor Vinyl Tape (B-595)

- Adheres to pipes, walls, equipment, windows – most clean, dry surfaces
- Conforms well to irregular, curved or rough surfaces
- Ideal for general purpose industrial uses – stands up to grease, oil and most industrial chemicals
- 8-10 year average outdoor durability in temperatures from 180°F to -40°F (82°C to -40°C) and can be applied as low as 0°F (-18°C)



Description	Catalog Number	Price Each
1/2" x 90'	142760	\$309.88
1 1/8" x 90'	142759	\$387.37
2 1/4" x 90'	142758	\$271.14
4" x 90'	142757	\$387.37


Description	Catalog Number	Price Each
1/2" x 90'	142750, 142769, 142777, 142745, 142772, 142741, 142756, 142785, 142781	\$309.88
1 1/8" x 90'	142765, 142749, 142768, 142776, 142744, 142773, 142740, 142755, 142784, 142793, 142787, 142790, 142780	\$387.37
2 1/4" x 90'	142764, 142748, 142767, 142775, 142743, 142771, 142739, 142754, 142783, 142792, 142786, 142789, 142779	\$271.14
3" x 90'	142747, 142738	\$314.25
4" x 90'	142763, 142746, 142766, 142774, 142742, 142770, 142737, 142753, 142782, 142791, 142788, 142778	\$387.37

Low-Halide Polyester Tape (B-569)

- Specially designed with a low halide content – best choice for use on stainless steel and nickel piping
- Applies best to smooth surfaces
- Has the same durability characteristics of the B-580 Indoor/Outdoor Vinyl Tape above

Description	Catalog Number	Price Each
1/2" x 110'	64326	\$431.27
1 1/8" x 110'	64327, 64331, 64335, 64339, 64347, 64355	\$541.62
2 1/4" x 110'	64328, 64332, 64336, 64340, 64348, 64356	\$381.10
4" x 110'	64329, 64333, 64349, 64357	\$541.62





Reflective Tape (B-584)

- Use both indoors and outdoors
- Reflective capabilities are ideal for reading labels in low light areas
- Locate labels from your vehicle with a flashlight
- 75 feet (22.9 m) per roll

Description		Catalog Number			Price Each
Tape Cartridges	No. Per Pkg.	Black	Black	Black	
1½" x 75'	2	64739	64400*	64403*	\$640.17
2¼" x 75'	1	64740	64401**	64404**	\$500.82
4" x 75'	1	64741	64402	64405	\$737.98

*Tape is 69' per roll. **Tape is 58' per roll.

Permanent Standard Tape (B-571)

- General use polyester tape with permanent adhesive
- Indoor use only
- 125 feet (38 m) per roll


Description		Catalog Number		Price Each
Size	Qty/Pkg.	Black	Black	
½" x 125'	2	64834	64842	\$330.92
1" x 125'	2	64835	64843	\$422.22
2" x 125'	1	64836	64844	\$284.80
3" x 125'	1	64923	64924	\$358.28
4" x 125'	1	64837	64845	\$421.22



Repositionable Vinyl Tape (B-581)

- Special adhesive allows easy removal of label with reapplication again and again
- Label of choice for indoor marking where frequent repositioning is required, such as storage shelves
- 90 feet (27.4 m) per roll

Tape Cartridge	No. Per Pkg.	Black	Black	Price Each
1½" x 90'	2	64731	64735	\$387.37
2¼" x 90'	1	64732	64736	\$271.14
4" x 90'	1	64733	64737	\$387.37



Cold Temperature Tape (B-549)

- Permanently adheres to surfaces at temperatures as low as -10°F (application temp.). Service temperature to -40°F
- Great for use in any cold storage warehouse, cooler or freezer
- Stands up to chemicals, water, oil and many solvents
- 90 feet (27.4 m) per roll

Tape Cartridge	No. Per Pkg.	Black	Black	Price Each
2" x 90'	1	64776	64685	\$279.36
3" x 90'	1	46237	46236	\$299.12
4" x 90'	1	—	64686	\$413.19

Removable Standard Tape (B-570)

- General use polyester tape can be used for indoor applications
- Label removes easily with no residue
- 110 feet (33.5 m) per roll

Description		Catalog Number			Price Each
Tape Cartridges	No. Per Pkg.	Black	Red	Blue	
½" x 110'	2	64838	—	—	\$324.64
1" x 110'	2	64839	64859	64863	\$413.19
2" x 110'	1	64840	64860	64864	\$279.36
3" x 110'	1	64926	64928	64929	\$351.96
4" x 110'	1	64841	64861	64865	\$413.19



Overlaminates (B-674)

- Provides improved label durability
- Hand applied after label is applied

Roll Size	Catalog No.	Price Each
¾" x 10 yards	25966	\$19.55
1⅜" x 10 yards	25967	\$25.32
2½" x 10 yards	25968	\$33.06
4¼" x 10 yards	25969	\$41.57

Other Printer Tapes, Ribbons and Tags

www.BradyID.com

GraphicsPro™ Tapes

Tapes & ribbons for the discontinued Graphics Pro™ Machine are still manufactured. The available parts are listed below.

Tapes	Size	Catalog No.	Price Each
White Vinyl Tape	4 ³ / ₈ " x 50'	36620	\$116.57
Yellow Vinyl Tape	4 ³ / ₈ " x 50'	36621	\$116.57
Red Vinyl Tape	4 ³ / ₈ " x 50'	36623	\$116.57
Blue Vinyl Tape	4 ³ / ₈ " x 50'	36624	\$116.57
Black Vinyl Tape	4 ³ / ₈ " x 50'	36626	\$116.57
White Reflective Tape	4" x 33'	36630	\$209.95

GraphicsPro™ Ribbons

Tapes & Ribbons	Size	Catalog No.	Price Each
Black Ribbon	4 ³ / ₈ " x 164'	36637	\$322.88

Premask	Size	Catalog No.	Price Each
Transfer paper for cut characters	5" x 164'	36635	\$116.57



Sign And Label Printers



Fastening Devices

- 32 mil stainless steel safety wire to be used with wire twister pliers.
- Standard package of 1800 feet

Catalog #	Description	Price
15424	Stainless Steel Safety Wire (1800 ft.)	\$46.02



Quik-ApPLY™ Nylon Straps

- Standard fastener for Quik-ApPLY™ pipe marker sizes Q1-Q4
- Can be used with a variety of tags including valve and lockout/tagouts

Catalog #	Outside Dia.	Strap Length	Price
91165	1"	6"	\$1.08
91166	2"	8"	\$1.26

Blank HPHV Carrier

- Ideal for marking custom markers on the spot
- Fiberglass carrier is blank (no label) and comes with two clips for installation
- Sized to accommodate the largest ASME (ANSI) requirements, 4.25" x 32"

Catalog #	Description	Price
59918	Blank HPHV Carrier	\$16.65

NEW!

Online Custom Design Tool

Design AMSE (ANSI) compliant Pipe Markers that meet the exact specification of your facility's pipes. Choose your style, size, color and custom text.

Try the Custom Design Tool at www.BradyID.com

Easy as 1, 2, 3!

- 1) Select your category
- 2) Customize your product
- 3) Add to your shopping cart



Create custom products in minutes!

Ships in 24-48 hours!



Make Your Own Valve Tags

- Use your Brady printer to apply labels to these durable tags
- Color Coded tags accepts round or flat fastening wire
- Withstands temperatures of -40°F (-40°C) to 180°F (82°C)
- Recessed area for label application on both sides of tag
- 1.5" x 3" Tag accepts labels 1.25" x 2.85" or smaller (use 1.25" or smaller tape on your Brady Printer)
- 2.5" x 4" Tag accepts labels 2.25" x 3.85" or smaller (use 2.25" or smaller tape on your Brady Printer)



Choose from ten bright colors.

Blank Plastic Valve Tags

Catalog Number	Color	Size	Price Each
41920	Black	1½" x 3"	\$2.18
41921	Black	2½" x 4"	\$2.36
41922	Yellow	1½" x 3"	\$2.18
41923	Yellow	2½" x 4"	\$2.36
41924	Red	1½" x 3"	\$2.18
41925	Red	2½" x 4"	\$2.36
41926	Blue	1½" x 3"	\$2.18
41927	Blue	2½" x 4"	\$2.36
41928	Green	1½" x 3"	\$2.18
41929	Green	2½" x 4"	\$2.36

Catalog Number	Color	Size	Price Each
87694	Orange	1½" x 3"	\$2.18
87695	Orange	2½" x 4"	\$2.36
87696	White	1½" x 3"	\$2.18
87697	White	2½" x 4"	\$2.36
87698	Grey	1½" x 3"	\$2.18
87699	Grey	2½" x 4"	\$2.36
87710	Brown	1½" x 3"	\$2.18
87711	Brown	2½" x 4"	\$2.36
87712	Tan	1½" x 3"	\$2.18
87713	Tan	2½" x 4"	\$2.36

Make Your Own BradySnap-On™ Pipe Markers

- Use blank BradySnap-On™ Pipe Markers (B-571 material) in combination with self-sticking pipe markers produced on your Brady HandiMark™, GlobalMark™, Labelizer Plus™ or PowerMark™ printers
- Create custom snap-on pipe markers on the spot!



Blank Snap-On Marker

Label produced on Brady Printer

Size	Fits Pipe Outside Diameter*	Length of Marker	Color				Price Each
			Yellow	Green	Red	Blue	
A	¾" to 1⅜"	8"	41900	41901	41902	41903	\$4.63
A2L	¾" to 1⅜"	16"	42300	42301	42302	42303	\$6.13
B	1½" to 2⅜"	9"	41904	41905	41906	41907	\$6.38
B2L	1½" to 2⅜"	16"	42304	42305	42306	42307	\$8.73
C	2½" to 3⅞"	13"	41908	41909	41910	41911	\$11.79
D	4" to 6"	21"	41912	41913	41914	41915	\$12.62
F/G	6" to 9⅞"	12"	42308	42309	42310	42311	\$13.04
H	10" to 15"	32"	42312	42313	42314	42315	\$23.29

*outside diameter includes pipe O.D. plus any insulation.

Blank High Performance Wrap-Around Pipe Marker

- Use Brady printers to create custom Wrap-Around Pipe Markers
- Self-sticking label can be applied directly to the Wrap-Around Pipe Marker surface



Size	Blue	Green	Red	Yellow	Price Each
Size I	57106	57102	57104	57100	\$9.59
Size II	57107	57103	57105	57101	\$13.75

MarkWare™ Facility Identification Software

www.BradyID.com

Software

Complete Labeling Solutions



www.BradyID.com/markware

MarkWare™ Facility Identification Software

Catalog Number: 20700

All Your Safety and Facility Needs in One Powerful Package.

- Use your PC to quickly design professional looking signs and labels
- Print directly to a Brady labeling system or most Windows™ inkjet/laser printers
- Preformatted templates make sign and label creation quick and easy - or, customize layouts to your own specs
- Import logos and photos or create bar codes using 15 different symbologies
- Link label contents to information stored in spreadsheets and databases
- Built-in library with over 1000 high-quality, scalable symbols and pictograms



Warning



Prohibition



Mandatory



First Aid



Fire Safety



Haz Chem



Public Info.



Tools



English & Foreign Language Headers

MarkWare™ Lean Tools Facility Identification Software

Catalog Number: 20700L

Includes all of the features and functionality of MARKWARE™ Facility Identification software, plus new tools to support and sustain your lean transformation. Post critical information at the point of use when implementing 5S, Total Productive Maintenance, Standard Work, Kanban, or other lean concepts.

- Achieve faster machine setups and changeovers.
- Simplify training of operators and other non-technical staff responsible for routine machine inspection and care.
- Enable more efficient route-based monitoring of numerous PM points in condition-based maintenance programs.



www.BradyID.com/markware

Sign & Label Blanks for MarkWare™ Software

- Adhesive backed polyester sign blanks are compatible for use with inkjet and laser printers



Description	Catalog #									Price
3½" x 5" (4 labels/sheet)	12906	12909	12912	12923	-	12900	12903	12926	\$71.01	
5" x 7" (2 labels/sheet)	12907	12910	12913	12922	-	12901	12904	12925	\$71.01	
7" x 10" (1 label/sheet)	12908	12911	12914	12921	13027	12902	12905	12924	\$71.01	

LabelMark™ Labeling Software

Brady's LabelMark™ Labeling Software offers features that make creating labels more efficient. Written specifically for identification applications in the telecommunication, laboratory and electrical markets where wire and cable marking is a constant and tedious job.

LabelMark labeling software is the easy solution for label design, editing and printing. LabelMark™ label making software is a fast system for creating new labels and printing professional, accurate and legible labels. With built-in templates, wizards, fixed text labels and free form design, LabelMark Label Software simplifies label making in the electrical, industrial, aerospace, laboratory, and telecomm industries.



www.BradyID.com/labelmark

InspectNTrack Software Equipment and Inspection Management Software

InspectNTrack is a web-based equipment management and inspection software that will help you schedule, track and document activities on any type of equipment or location. Used with or without Pocket PCs, it's the ideal solution for compliance-based inspections regulated by any authority having jurisdiction (AHJ).

InspectNTrack tracks activities for equipment or checkpoints that require regular inspection intervals. InspectNTrack eliminates paper forms by providing the ability to perform inspections using a handheld Pocket PC. The Pocket PC directs the user to the exact location of the checkpoint. With the Pocket PC the user has the ability to scan barcodes, pass/fail inspections and trigger incidents. The user can gather detailed data using Question and Incident Sets. InspectNTrack also provides the ability to organize inspections by Customers and Routes.

As a web-based program, InspectNTrack can be accessed at any time from any computer with internet access. The system ensures on-time, accurate inspections and eliminates missed inspections.

Easily create, maintain, and update records such as:

- Individual Users
- Inspection Checkpoints
- Assign tasks and task intervals
- Maintain checkpoint records
- Organize checkpoints into routes and zones
- One or multiple sites

Review, analyze and track data with reports, including:

- History reports displaying work that has been completed
- Detailed Inspections
- When the inspection was last performed
- What the user visited and documented, including any incidents triggered
- All open or closed discrepancies

InspectNTrack is available in a standard version with three checkpoint levels to choose from or an enterprise version that supports unlimited checkpoints and multiple sites.



! **For More Information**
www.BradyID.com/InspectNTrack

Lockout PRO™ Graphical Procedure Writing Software

Brady Lockout PRO™ 3.0 Enterprise Graphical Procedure Writing Software provides all the tools you need to create an effective, compliant energy control program with standardized procedures that are easy to follow. Lockout tags and labels can be printed for each energy source and are cross-referenced to the procedure, making lockout activities virtually foolproof.



www.BradyID.com/lockoutpro

NetDoc™ Network Documentation

NetDoc® Network Cable Management Software provides you with the tools you need to manage cabling, network, telephony and legacy connections. NetDoc® allows you to easily document horizontal and backbone cables, hardware, assets, pathways, locations, users and much more! The NetDoc® web-enabled solution provides complete ANSI/TIA/EIA 606A documentation compliance. And, its seamless integration with Brady's LabelMark™ label design software gives you a complete documentation and labeling solution to help increase productivity, reduce costs, and improve user services!



www.BradyID.com/netdoc

! **More Information**
 For more information on any of the software programs listed, visit www.BradyID.com and search by the software name.

Brady BLS1255 Laminator

www.BradyID.com

Laminators



Laminates documents up to 12" wide!

BLS1255 Laminating System

Quickly mount PowerMark™ output to plastic or aluminum sign blanks...takes only seconds!

Laminating Options:

- Mount label to a rigid plastic or aluminum sign panel
- Mount label behind a rigid, clear acrylic sign panel to add rigidity while protecting the graphics...polished look for office areas
- Overlaminates documents with a single or double-sided flexible, clear overlaminates

BLS1255 Laminating System

Description	Catalog Number	Price Each
BLS1255 Laminating System	105038	\$421.95

BLS1255 Clear Overlaminates - 50' length

Description	Catalog Number	Price Each
12" Double-sided polyester overlaminates	105041	\$150.00

Sign blanks to mount output from PowerMark™ printer

Plastic - rounded corners and hole punched - sold 10/pkg

Size	White	Yellow	Orange	Price Each
4.25" x 6.25"	13620	13621	13622	\$14.48
7.63" x 10.38"	13623	13624	13625	\$31.92
10.25" x 14.25"	13626	13627	13628	\$46.47

Aluminum - rounded corners and hole punched - sold 10/pkg

Size	White	Yellow	Orange	Price Each
4.25" x 6.25"	13629	13630	13631	\$40.10
4.25" x 10.25"	106461	—	—	\$29.29
7.25" x 10.25"	13632	13633	13634	\$53.95
7.63" x 10.38"	106460	—	—	\$67.62
10.25" x 10.25"	106462	—	—	\$53.66
10.25" x 14.25"	13635	13636	13637	\$78.90

Clear acrylic panels with pressure sensitive adhesive* (sign panel and overlaminates in one step) — sold 10/pkg.

Size	Catalog Number	Price Each
4" x 6"	13638	\$43.58
4.25" x 10.25"	106464	\$31.54
7.25" x 10"	13639	\$58.11
7.25" x 10.25"	106463	\$74.74
10" x 14"	13640	\$87.18
10.25" x 10.25"	106465	\$58.96

*Use to mount output behind a clear panel to add rigidity while protecting the graphics...polished finish for office areas.

**No Heat!
No Electricity!
No Messy
Chemicals!**

Mount PowerMark™ output to plastic or aluminum sign panels in 3 easy steps!



Step 1: Peel away the first 1 1/2" of liner from the back of PowerMark™ printer output. Apply to blank panel, aligning edge of label with edge of panel.



Step 2: Insert sign into laminator and rotate handle until first 1" of sign is "pinched".

Stop. Then grasp liner of sign and pull at the same time as you rotate handle rapidly advancing sign through the laminator.



Step 3: In less than 30 seconds you have a rigid sign ready to hang. Choose from aluminum, plastic or clear acrylic panel materials.



Use the BLS1255 laminator to mount your PowerMark™ output to a rigid plastic or aluminum panel...in seconds.

BLS850 Laminating System

- An affordable and easy way to create laminated documents up to 8½" wide without heat or electricity
- Laminate documents in seconds
- Perfect for office use or industrial applications
- Small, portable desktop laminator works without electricity, heat or messy chemicals
- Economically priced Applications are endless



**No Heat!
No Electricity!
No Problem!**

Features

- Three replaceable supply cartridge types (double-sided laminate, single-sided overlaminate, laminate with transfer adhesive)
- Integral cut-off blade at roller exit
- Laminates documents 8½" wide and up to 100' long
- Small, lightweight and portable
- Laminates with Brady's EXCLUSIVE industrial grade laminate!
- Brady's exclusive industrial grade overlaminate is constructed from tough polyester for durability even in harsh environments
- Significantly superior to typical polypropelene overlaminates in terms of outdoor performance and abrasion resistance

BLS850 Laminating System

Description	Catalog Number	Price Each
BLS850 Laminator	20585	\$147.65

BLS850 Clear Overlaminates

Description	Supply Sizes	Catalog Number	Price Each
Double-sided/Industrial use	8¾" x 50' (21.8 cm x 15.2 m)	20589	\$133.95
Double-sided/Office use	8¾" x 100' (21.8 cm x 30.5 m)	20602	\$81.84

* Overlamine on one side, transfer adhesive on the other side.

Use a BLS850 to finish:

- Signs
- Graphs
- ID Badges
- Maps
- Tags
- Procedures
- Labels
- Certificates
- ISO Documents
- Photos
- Wall Charts
- Phone Lists

Need to laminate documents wider than 8½"? See the BLS1255 on the previous page.

Brady's Easy-to-Use BLS850 Laminator Covers it All



1. Select desired cartridge, insert a document and turn the handle.



2. As it passes through the rollers, the adhesive and laminate are evenly applied.




3. The cut-off blade provides a precise trim to finish documents.



Provides the perfect finishing touch for your Brady printer.



Laminator allows you to laminate one side of document while applying adhesive to reverse.




Laminate your most frequently reached for documents.

Sorbents and Spill Control

www.BradyID.com/spc

How Do You Choose A Sorbent?

Actually, start at the end, in the trash. One of the best ways to help you pick the right sorbent is to see what they look like when you're done with them. Take a look...




These sorbents are being used in a traffic area – choose a tough sorbent like **BattleMat™** or one of our HT rolls to get durability and high absorbency.



Too much sorbent for the application. Save some money by choosing a medium or lightweight pad.



Not Enough Sorbent! Consider a heavyweight pad to increase performance and cut down on the number of lighter pads you go through everyday. Start with **MRO-100**. Or go GREEN with Re-Form! The RFP100 Re-Form Plus pad made from recycled cellulose materials, is up to 50% more absorbent.



Looks like this sorbent is containing a leak – consider using a **SOC** for containing leaky equipment. SPC offers a variety of SOC's to meet your needs.



Did You Know?

There is a negative financial impact of using clay to clean up your leaks, drips and spills. It may be cheaper to buy, but the benefits stop there. For example, a facility that uses sorbents to clean up 32 gallons of oil on average each month may expect to spend as follows*:

Using Clay:

- 8 - 30lb. bags @ \$9 each = \$72
- 2 disposal drums @ \$350 each = \$700
- Total spend = \$772

Using SPC Sorbents

- 1 bale of pads @ \$76 = \$76
- 1 disposal drum @ \$350 = \$350
- Total spend = \$426

A 45% SAVINGS WITH SPC

Still not convinced? Consider these points:

- OSHA considers silica a serious health hazard.
- Granular clean-up is difficult and labor intensive.
- The small particles can easily enter and damage machinery or your finished product.
- Clay has limited chemical resistance.
- WITH SPC, ALL OF THESE SHORTCOMINGS ARE ELIMINATED



* This is a basic analysis using estimations and averages. Individual situations will vary. Contact your BRADY/SPC Regional Sorbent Sales Manager to do a more in-depth and customized analysis of your costs.



Important Related OSHA and EPA Regulations

29 CFR 1910.22(a)(2)

Clean, dry workplace floors.

40 CFR 112.7(c)(1)(vii)

Sorbent materials are one option for preventing oil spills from reaching waterways

29 CFR 1910.120(j)(1)(vii)

DOT-specified containers and suitable quantities of absorbents shall be kept available for response to spills



Spill Prevention Control & Countermeasure (SPCC) Plan

The EPA issued its final rule amending the SPCC under the authority of the Federal Water Pollution Control Act. This regulation became effective as of August 16, 2002.

What is an SPCC Plan?

An SPCC Plan is a facility-specific comprehensive description of a facility's containment and counter measures that would prevent an oil spill from occurring as well as procedures to respond and clean up an oil spill that does occur.

The SPCC plan addresses the following three areas:

- Operating procedures that prevent oil spills
- Control measures installed to prevent a spill from reaching the environment
- Countermeasures to contain, clean up, and mitigate the effects of an oil spill that reaches the environment



Did You Know? SPC offers a FREE Facility Environmental Survey

Surveying a facility for potential trouble spots, proper sorbent usage and product selection can be extremely beneficial. For example, environmental and site surveys uncover excellent opportunities for product standardization and consolidation, especially at larger plants where various departments buy sorbents from different sources. As a value-added service, SPC and its distributors can help plants make better application decisions and reduce costs.

Environmental Survey

SPC's Environmental Survey is a free service – helping facilities keep their employees and their equipment clean and safe, while coming into compliance with OSHA, EPA and SPCC regulations. This detailed survey asks the right questions and identifies the way in which SPC and its distributor can provide solutions for the proper use of sorbents in the plant. Many organizations use these surveys as an "Environmental Audit" and keep them on file.

Cost Savings Worksheet

Seeing is believing! This simple worksheet helps you compare the sorbents you are currently buying with our recommendations – automatically calculating the price difference and displaying your cost savings.

Cross Reference

This web-based tool allows you to quickly choose which SPC sorbent products are the best alternative to the ones you may be currently using. You can find it at www.BradyID.com/spc. Click on the manufacturer; then select the product being used. you'll quickly learn which SPC products can be use to do the best job for you. Our website is fully functional information resource Center both your spill containment and greater safety and identification needs.



Re-Form™ Eco-Friendly Sorbents

www.BradyID.com/spc

Sorbents and Spill Control



Re-Form™ Eco-Friendly High Performance Sorbents.
A new generation of green sorbents that will reform your thinking.



Green to produce. Green in use. The production process used for Re-Form™ sorbent material takes less away from our environment. Re-Form sorbents are made from a minimum of 80% recycled newsprint and other cellulose for Universal products and 80% cotton and other cellulose fibers for Oil-Only products. And, the better absorbency of Re-Form means you'll have less waste.

Better Absorbency The unique construction of Re-Form™ sorbent material offers superior absorbency. In fact, Re-Form sorbents have been tested to be 25-50% more absorbent than oil-based polypropylene sorbents, so you'll use less product to get the job done. Less waste makes this sorbent both green and lean!

UP TO
**50%
MORE
ABSORBENT**



Satisfaction Guarantee

Test the superior absorbency for yourself - your initial case comes with a money back guarantee!

Cost Savings. Re-Form will also put some green in your pocket. Re-Form sorbents are typically less expensive than polypropylene sorbents which are oil based and dependant upon volatile oil prices.

Re-Form's Eco-Friendly Family Of High-Performance Sorbents:



Re-Form

Universal sorbent made from recycled newsprint and cellulose.

- Netted construction
- Quick clean up for drips and spills
- Indoor or dry weather outdoor use



Re-Form Plus

Same as Reform Universal with abrasion resistant coverstock on one side.

- Perfect for drips, spills and wiping applications around machines and equipment
- Spunbound coverstock on 1 side withstands moderate foot traffic
- Indoor or dry weather outdoor use



Re-Form XPlus

Same as Reform Universal with tough abrasion resistant coverstock on two sides for extra durability.

- Spunbound coverstock on 2 sides
- Ideal for foot traffic and wiping applications
- Indoor or dry weather outdoor use



NEW!

Re-Form Oil Only

Oil Only sorbent absorbs petroleum based liquids, grease, transmission fluids and coolant.

- Great for outdoor oil/fuel storage area
- Durable spunbound coverstock on 2 sides for pads, and on 1 side for rolls
- Repels water and floats - ideal for marine applications and spills
- Available in weather resistant bags

*Note: Re-Form™ Sorbents are not intended for use with highly aggressive chemicals.

Re-Form™ Eco-Friendly Sorbents

www.BradyID.com/spc

Sorbents and Spill Control



Re-Form™ Sorbent Pads

- Ideal for drips, spills and wiping applications
- Available in universal and oil only Re-Form
- Spunbound coverstock on 1-2 sides

Re-Form Pads

Catalog #	Description	Size	Absorbency	Qty/Case	Price
RF100	Re-Form Heavy WT. Pad	15" x 19" (38.1 x 48.3cm)	40 (151L)	100	\$81.45
RF300	Re-Form Medium WT. Pad	15" x 19" (38.1 x 48.3cm)	32 (121L)	100	\$68.85
RF500	Re-Form Light WT. Pad	15" x 19" (38.1 x 48.3cm)	24 (90L)	100	\$54.30

Re-Form Plus Pads (1-side coverstock)

Catalog #	Description	Size	Absorbency	Qty/Case	Price
RFP100	Re-Form Plus Heavy WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	40 (151L)	100	\$87.27
RFP300	Re-Form Plus Medium WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	32 (121L)	100	\$73.69
RFP500	Re-Form Plus Light WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	24 (90L)	100	\$60.12

Re-Form XPlus Pads (2-side coverstock)

Catalog #	Description	Size	Absorbency	Qty/Case	Price
RFDP300	Re-Form XPlus Medium WT. Pad	15" x 19" (38.1 x 48.3cm)	32 (121L)	100	\$83.39

Re-Form Oil Only Pads (2-side coverstock) **NEW!**

Catalog #	Description	Size	Absorbency	Qty/Case	Price
RFODP100-B	Re-Form Oil Only Heavy WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	39 (148L)	100/bag	\$71.56
RFODP100	Re-Form Oil Only Heavy WT. Pad, Perforated	15" x 19" (38.1 x 48.3cm)	39 (148L)	100	\$74.18



Re-Form™ Sorbent Rolls

- Ideal for drips, spills and wiping applications
- Available in universal and oil only Re-Form
- Spunbound coverstock on 1-2 sides

Re-Form Plus Rolls (1-side coverstock)

Catalog #	Description	Size	Absorbency	Qty/Case	Price
RFP14P	Re-Form Plus Heavy WT. Roll, Perforated	14.25" x 150' (36.2cm x 45.7m)	30 (113L)	1	\$91.15
RFP28-DP	Re-Form Plus Heavy WT. Roll, Dbl Perf'ed	28.5" x 150' (72.4cm x 45.7m)	62 (234L)	1	\$151.27
RFP314P	Re-Form Plus Medium WT. Roll, Perforated	14.25" x 150' (36.2cm x 45.7m)	29 (109L)	1	\$69.82
RFP328-DP	Re-Form Plus Medium WT. Roll, Dbl Perf'ed	28.5" x 150' (72.4cm x 45.7m)	53 (200L)	1	\$120.24

Re-Form XPlus Rolls (2-side coverstock)

Catalog #	Description	Size	Absorbency	Qty/Case	Price
RFDP314P	Re-Form XPlus Medium WT. Roll	14.25" x 150' (36.2cm x 45.7m)	27.5 (104L)	1	\$85.34
RFDP328-DP	Re-Form XPlus Medium WT. Roll	28.5" x 150' (72.4cm x 45.7m)	55 (208L)	1	\$145.46

Re-Form Oil Only Rolls (2-side coverstock) **NEW!**

Catalog #	Description	Size	Absorbency	Qty/Case	Price
RFOP14P	Re-Form Oil Only Heavy WT. Roll, Perforated	14.25" x 150' (36.2cm x 45.7m)	37 (141L)	1	\$62.84
RFOP28-DP	Re-Form Oil Only Heavy WT. Roll, Dbl Perf'ed	28.5" x 150' (72.4cm x 45.7m)	74 (282L)	1	\$115.20



Re-Form™ Sorbent SOCs

- Routine spill containment and control
- Universal economy SOC
- Oil-only SOC repels water

Re-Form Multiwick SOCs

Catalog #	Description	Size	Absorbency	Qty/Case	Price
MS-50	Re-Form Multiwik Soc	3" x 4' (76mm x 1.2m)	40 (151L)	40	\$116.77
MS-412	Re-Form Multiwik Soc	3" x 4' (76mm x 1.2m)	12 (45L)	12	\$57.22
MS-806	Re-Form Multiwik Soc	3" x 8' (76mm x 2.4m)	12 (45L)	6	\$57.22
MS-124	Re-Form Multiwik Soc	3" x 12' (76mm x 3.6m)	12 (45L)	4	\$57.22

Re-Form Oil Only SOCs **NEW!**

Catalog #	Description	Size	Absorbency	Qty/Case	Price
RF0412	Re-Form Oil Only Soc	3" x 4' (76mm x 1.2m)	15 (56L)	12	\$61.96



Re-Form Oil Only Booms and Re-Form Granular available on page 168.

*Note: Re-Form™ Sorbents are not intended for use with highly aggressive chemicals.

Universal Sorbents

www.BradyID.com/spc

Sorbents and Spill Control

Universal Pads and Rolls

Use these all-purpose sorbents to clean up oils, coolants, solvents and water-based fluids anywhere in your facility. Around machinery, under leaky pipes or fittings, in messy traffic areas, for general maintenance projects – they are your first choice for indoor spill control. Plus, their gray color masks spills and stains – helping you resist the urge to pick up the sorbent before it is fully saturated.




MRO Plus Sorbents

- Standard in all-purpose, gray maintenance sorbents
- Three-ply construction makes it stronger, more durable and reduces lint

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
MRO100*	Pad	15" x 19"	100/case	\$110.59
MRO100-B*	Pad	15" x 19"	100/bale	\$110.59
MRO100-2*	Pad	15" x 19"	50/bale	\$59.13
MRO50	Pad	30" x 30"	50/bale	\$179.34
MRO150DND**	Pad	15" x 19"	150/case	\$155.89
MRO15	Roll	15" x 150'	1/case	\$126.39
MRO15P*	Roll	15" x 150'	1/case	\$132.69
MRO15DP*	Roll	15" x 150'	1/case	\$136.02
MRO15DPS	Roll	15" x 73'	1/bale	\$68.14
MRO24DP*	Roll	24" x 150'	1/bale	\$168.97
MRO30	Roll	30" x 150'	1/case	\$197.12
MRO30P*	Roll	30" x 150'	1/case	\$203.79
MRO30DP*	Roll	30" x 150'	1/case	\$206.87
Medium Weight				
MRO300*	Pad	15" x 19"	100/case	\$87.51
MRO315P*	Roll	15" x 150'	1/case	\$90.47
MRO350DP*	Roll	30" x 150'	1/case	\$144.66

*Perforated to help you use only what you need
 **Dispense-n-dispose system, also perforated.



Battlemat™ Sorbents

- Tough construction; ideal as walk-on mat
- Camouflage-print masks spills and soils

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
BM15**	Roll	15" x 150'	1/case	\$142.69
BM30**	Roll	30" x 150'	1/case	\$281.92
BM30X	Roll	30" x 150'	1/case	\$281.92
BM100*	Pads	15" x 19"	100/bale	\$151.20

*Perforated
 **Double perforated




UXT™ Xtra Tough Sorbents

- High performance sorbents made to handle virtually any liquid
- Spunbound coverstock on both sides for maximum durability

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
UXT100*	Pads	15" x 19"	100/case	\$102.82
UXT15P*	Roll	15" x 150'	1/case	\$107.63
UXT30DP**	Roll	30" x 150'	1/case	\$191.69
Medium Weight				
UXT300	Pad	15" x 19"	100/case	\$102.82
Light Weight				
UXT200*	Pads	15" x 19"	200/case	\$110.59

*Perforated
 **Double perforated




HT Series Sorbents

- Economical for high traffic areas
- 2-ply construction makes it stronger
- Durable, abrasion-resistant

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
HT15*	Roll	15" x 150'	1/case	\$137.26
HT555**	Roll	15" x 150'	1/case	\$129.72
HT30**	Roll	30" x 150'	1/case	\$207.37
HT550***	Roll	5" x 50'	1/case	\$38.33
Medium Weight				
HT153*	Roll	15" x 300'	1/bale	\$132.81
HT303X	Roll	30" x 300'	1/bale	\$212.18
HT303**	Roll	30" x 300'	1/bale	\$212.18
HT350**	Roll	30" x 150'	1/bale	\$127.15

Light Weight
 HT215 Roll 15" x 300' 1/bale \$93.34
 HT230** Roll 30" x 300' 1/bale \$168.90
 *Perforated **Double perforated ***Triple Perforated



GP™ Sorbents

- General purpose, single-ply dimpled construction
- Made with exclusive MAXX technology
- MXU1000 absorbs up to 23x its weight in oil

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
GP100	Pads	15" x 19"	100/case	\$92.08
GP100-B	Pads	15" x 19"	100/bale	\$92.08
GP30	Roll	30" x 150'	100/bale	\$161.69
Medium Weight				
GP300	Pads	15" x 19"	100/bale	\$75.00
Light Weight				
GP200	Pads	15" x 19"	200/bale	\$96.03
GP200-B	Pads	15" x 19"	100/bale	\$92.08
GP500	Pads	15" x 19"	100/bale	\$56.77
MXU1000	Pads	15" x 19"	100/bale	\$59.24



Basic™ Sorbents

- Economical single ply construction for drips and spills

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
BPU100	Pad	15" x 17"	100/bale	\$47.00
BPU200	Pad	15" x 17"	200/bale	\$62.00
BRU150	Roll	30" x 150'	1/bale	\$110.00
Light Weight				
BPU500	Pad	15" x 17"	100/bale	\$37.78
BHT150	Mat	30" x 150"	1/bale	\$108.00

Oil Only Pads and Rolls

Specialized for oil and other petroleum-based spills, oil only pads and rolls will not absorb water and will float indefinitely. These sorbents are unaffected by temperature and impervious to rot and mildew and are ideal for outdoor use. Oil only products are equally effective in soaking up petroleum-based solvents and paints, vegetable oils and other non-water soluble chemicals.



ENV Series Sorbents

- Contractor grade oil-only sorbents made with exclusive MAXX technology
- Efficient, non-dimpled single-ply construction absorbs petroleum-based liquids but repels water

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
ENV100	Pads	15" x 19"	100/bale	\$76.16
Medium Weight				
ENV150	Roll	30" x 150'	1/bale	\$117.26
ENV300	Pads	15" x 19"	100/bale	\$62.83
ENV50	Pads	30" x 30"	50/bale	\$132.32
Light Weight				
ENV200	Pads	15" x 19"	200/bale	\$80.10
ENV500	Pads	15" x 19"	100/bale	\$46.91
MXO1000	Pads	15" x 19"	100/case	\$49.37



SXT™ Sorbents

- Oil only sorbent made to handle petroleum-based spills
- Multi-ply w/ spunbound coverstock both sides

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
SXT100	Pads	15" x 19"	100/case	\$88.50
SXT15P*	Roll	15" x 150'	1/case	\$93.56
SXT30DP*	Roll	30" x 150'	1/case	\$145.03
Medium Weight				
SXT300	Pad	15" x 19"	100/case	\$72.91
Light Weight				
SXT200	Pads	15" x 19"	200/case	\$103.56

*Perforated



Oil Plus Sorbents

- Multi-ply, heavyweight quality you can count on
- Dimpled and perforated to help you use only what you need

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
OP100	Pad	15" x 19"	100/case	\$98.01
OP100X-B**	Pad	15" x 19"	1/bale	\$98.01
OP150DND†	Pad	15" x 19"	150/case	\$142.81
OP550	Roll	15" x 50'	1/case	\$44.06
OP15	Roll	15" x 150'	1/case	\$116.64
OP15P*	Roll	15" x 150'	1/case	\$123.07
OP15DP*	Roll	15" x 150'	1/case	\$126.39
OP15DPS*	Roll	15" x 73"	1/bale	\$65.05
OP30	Roll	30" x 150'	1/case	\$180.95
OP30P*	Roll	30" x 150'	1/case	\$187.49
OP30DP*	Roll	30" x 150'	1/case	\$190.82
OP50	Pad	30" x 30"	50/bale	\$160.09
Medium Weight				
OP300	Pad	15" x 19"	100/case	\$84.55
OP315P*	Roll	15" x 150'	1/case	\$87.51
OP350DP*	Roll	30" x 150'	1/case	\$140.46

*Perforated **Undimpled ***Triple Perforated
†Dispense-n-dispose system



Basic™ Oil Only Sorbents

- Economical single ply construction for drips and spills

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
BP0100	Pad	15" x 17"	100/case	\$41.66
BR0150	Roll	30" x 150'	1/case	\$102.00
Light Weight				
BP0200	Pad	15" x 17"	200/case	\$58.00
BP0500	Pad	15" x 17"	100/case	\$33.00



SPC Series Sorbents

- Heavier and bonded to enhance strength and reduce linting
- Dimpled and perforated, single-ply.
- Made with exclusive MAXX technology and ideal for outdoor applications

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
SPC100	Pads	15" x 19"	100/bale	\$94.92
SPC50	Pads	33" x 39"	50/bale	\$219.71
SPC150	Roll	38" x 144'	1/bale	\$203.66
SPC152	Roll	19" x 144'	2/bale	\$214.15
Medium Weight				
SPC300	Roll	15" x 19"	100/bale	\$79.99
Light Weight				
SPC200	Pads	15" x 19"	200/bale	\$106.76
SPC500	Pads	15" x 19"	100/bale	\$60.11



Static Resistant

- Treated to resist static electricity build up
- Oil only - does not absorb water
- Meets NFPA specifications

Cat. No.	Type	Size	Qty.	Price
Heavy Weight				
SR100	Pad	15" x 19"	100/bale	\$81.66
SR1825	Pads	15" x 19"	25/bale	\$36.54
SR1850	Pads	15" x 19"	50/bale	\$37.52
SR50	Pad	30" x 30"	50/bale	\$129.77
SR3625	Pads	30" x 30"	25/bale	\$82.33
Light Weight				
SR3600	Roll	30" x 150'	1/bale	\$173.17

Chemical Sorbents

www.BradyID.com/spc

Sorbents and Spill Control

Chemical Pads and Rolls

These surfactant-treated polypropylene pads and rolls can be used on a wide range of chemicals, including hydrofluoric acid and are chemically inert, so they will not react with aggressive fluids.



MAXX Chemical

- Yellow color for safety and identification
- Product will not react with aggressive fluids

Cat. No.	Type	Size	Qty.	Price
CH1212	Pads	12" x 12"	200/case	\$120.97
CH100	Pads	15" x 19"	100/case	\$111.09
HAZ100-7	Pads	7.5"x34"	400/case	\$227.09
CH15P*	Roll	15" x 150"	1/case	\$96.28
CH30DP*	Roll	30" x 150"	1/case	\$195.02

*Perforated



Universal Plus

- Green universal sorbent for any liquid including oil, hazardous chemicals & acids
- Chemically inert makes it ideal for aggressive fluids

Cat. No.	Type	Size	Qty.	Price
UN1113	Pads	12" x 12"	200/case	\$158.36
UN1719*	Pads	15" x 19"	100/case	\$162.19
UN1019*	Roll	15" x 150"	2/case	\$237.61
UN3800*	Roll	30" x 150"	1/case	\$237.61
UN5200*	Roll	7.5"x200"	1/case	\$92.71

*Perforated



Maxx Packs


- Mini-packs in re-sealable zipper bags
- 20 economic, single ply pads

Cat. No.	Type	Size	Qty.	Price
MXP-U20	Universal	15" x 19"	20	\$122.11
MXP-O20	Oil Only	15" x 19"	20	\$122.11
MXP-C20	Chemical	15" x 19"	20	\$133.22

5 per case

Mats and Rugs

Increase safety in the workplace with absorbent industrial mats and rugs for heavy traffic areas and workstations.



Barrier Spill Matting

- Industrial rug made from needle-punched polypropylene
- Non-slip backing sticks to the floor and prevents fluids from leaking through to the floor
- Absorbs water, oil or chemicals


Cat. #	Type	Size	Qty.	Price
BSM100	Roll	36" x 100'	1	\$259.46
BSM300	Roll	36" x 300'	1	\$696.40
BSM3650	Roll	36" x 50'	1	\$186.88



Sorbent Industrial Rug

- Made of durable, needle-punched polypropylene fibers
- Eliminates slippery areas and unsightly tracking
- Can stand up to most aggressive fluids

Cat. #	Type	Size	Qty.	Price
SIR36	Roll	36" x 300'	1	\$379.93
SIR36150	Roll	36" x 150'	1	\$103.00
SIR72	Roll	72" x 150'	1	\$379.93



Rag Rug & Pad

- Economy rug made from recycled cotton and polyester
- Provides good footing, masks dirt and absorbs spills
- Soaks up oil, water-based and solvent-based liquids

Cat. #	Type	Size	Qty.	Price
RAG1818	Pad	18" x 18"	10	\$75.38
RAG36150	Roll	36" x 150'	1	\$188.61



TRACKMAT™ Roll

- 3-ply construction for high volume petroleum spills
- Non-leaking and non-slip barrier backing
- The most absorbent barrier mat available

Cat. #	Type	Size	Qty.	Price
TM58	Roll	58" x 80'	1	\$467.44

SOCS and Pillows

- Dependable, flexible tubes that contain and absorb
- Molds around corners and conforms to uneven surfaces
- Available in a wide variety of types and sizes
- Everyday working tool for all major industries



Before SOC Application



After SOC Application



Re-Form™ SOCS

- Made from recycled newsprint and other cellulose and up to 50% more absorbent than polypropylene and still repel water.

Re-Form™ Multiwick SOC

Cat. No.	Desc.	Size	Qty.	Price
MS-50	SOC	3" x 4'	40	\$116.77
MS-412	SOC	3" x 4'	12	\$57.22
MS-806	SOC	3" x 8'	6	\$57.22
MS-124	SOC	3" x 12'	4	\$57.22

Re-Form™ Oil Only SOC

Cat. No.	Desc.	Size	Qty.	Price
RF0412	SOC	3" x 4'	12	\$71.00



ALLWIK® SOC

- All-purpose polypropylene SOC
- Suitable for most industrial applications
- Wringable and incinerable

Cat. No.	Type	Size	Qty.	Price
AW430	Soc	3" x 4'	30/case	\$142.69
AW412	Soc	3" x 4'	12/case	\$88.87
AW806	Soc	3" x 8'	6/case	\$88.87
AW124	Soc	3" x 12'	4/case	\$88.87



SLIKWIK® SOC

- Corncob-filled SOC
- For use on all fluids except aggressive ones

Cat. No.	Type	Size	Qty.	Price
SW46	Soc	3" x 42"	40/case	\$103.93



Oil Only SOC

- Oil-only polypropylene SOC
- Will not absorb water-based solutions
- Wringable and incinerable

Cat. No.	Type	Size	Qty.	Price
OIL430	Soc	3" x 4'	30/case	\$163.18
OIL412	Soc	3" x 4'	12/case	\$84.06
OIL806	Soc	3" x 8'	6/case	\$84.06
OIL124	Soc	3" x 12'	4/case	\$84.06



HAZWIK® SOC

- Chemical clean-up polypropylene SOC
- Color-coded green for safety
- Wringable and incinerable

Cat. No.	Type	Size	Qty.	Price
HAZ412	Soc	3" x 4'	12/case	\$103.31
HAZ124	Soc	3" x 12'	4/case	\$103.31



Cobra Coil SOC

- Excellent for diking, SOC filled with granular absorbent
- Suitable for most fluids

Cat. No.	Desc.	Size	Qty.	Price
CC400	SOC	3" x 4"	12	\$72.21



Pillows

- Oil only pillows for oil based liquids
- Allwik® pillows absorb all oil and water-based fluids
- Hazwick® pillows are for hazardous materials

Oil Only Pillows

Cat. No.	Size	Qty.	Price
OIL99	9" x 9"	32/case	\$119.48
OIL1818	18" x 18"	16/case	\$103.56

AllWik® Pillows

Cat. No.	Size	Qty.	Price
AW99	9" x 9"	32/case	\$123.07
AW1818	18" x 18"	16/case	\$103.56

HazWik® Pillows

Cat. No.	Size	Qty.	Price
HAZ99	9" x 9"	32/case	\$129.48
HAZ1818	18" x 18"	16/case	\$111.09



Storm Drain Guards

- Keep oil, sediment and other contaminants from entering the water system
- Made from non-woven polypropylene
- Holds up to 40lbs of sediment. Flow rate is 500 gpm (new) and 700 gpm bypass.
- X-TEX filter strips increase absorbency.

Storm Drain Guards (Includes 4 handling straps)

Cat. No.	Size	Qty.	Price
DGUARD9	36" x 48" x 18"	1/case	\$115.84
DGUARD14*	36" x 48" x 18"	1/case	\$172.40
DGUARD910	36" x 48" x 18"	10/case	\$1,132.42
DGUARD1410*	36" x 48" x 18"	10/case	\$1,597.92

*With X-TEX filter strips


Marine and Loose Granular Sorbents

www.BradyID.com/spc

Sorbents and Spill Control

Marine Sorbents


Specifically designed for cleaning up oil spills on the water.



Sorbent Booms

- Premium SPC booms are lint free and easy to handle
- Economical ENV™ booms feature a lint-free blue sleeve

Cat. No.	Type	Size	Qty.	Price
RF0510	Re-Form Boom	5" x 10"	4	\$105.67
RF0810	Re-Form Boom	8" x 10"	4	\$135.62
SPC810	Boom	8" x 10"	4	\$282.90
SPC510	Boom	5" x 10"	4	\$149.84
SPC5510	Boom	5" x 10"	2	\$295.61
SPC318	Bilge Boom	3" x 18"	10	\$96.40
SPC518	Bilge Boom	5" x 18"	10	\$102.81
SPC818	Bilge Boom	8" x 18"	10	\$127.02
ENV810	Boom	8" x 10"	4	\$155.40
ENV510	Boom	5" x 10"	4	\$121.08



Sweep & Pillows

- "Sweeps" the water to remove surface oil and clean up a spill. 100' sections for dragging behind or connecting between ships.
- Marine Jumbo Pillow enclosed in a heavy duty netting

Cat. No.	Type	Size	Qty.	Price
SPC1900	Sweep	19" x 100'	1	\$149.84
SPC10	Pillows	14" x 25"	10	\$153.18



Oil Drag Net

- Floats in water to entrap oil
- Can be re-used after draining or dousing with #1 or #2 weight oils
- Use as a sweep between boats or deployed along shore

Cat. #	Type	Size	Qty.	Price
ODN08	Drag Net	50' (30 nets)	2/bale	\$135.78

Loose Granular Multi-Purpose Absorbents

Multi-purpose absorbents for spill clean-up, lab packing and stabilization of free liquids.



Dri-Zorb

- All natural corncob product for oil, grease, water and other liquids.
- Ideal for use in aircraft maintenance, machine shops, food processing, filling lines and bulk liquid transfer stations.
- Not for use with aggressive fluids

Cat. No.	Type	Qty.	Price
DZ100	40lb Bags	40 bags/pallet	\$627.20



Oil Gator® Granular

- All natural biodegradable absorbent captures 2-6 times its weight in oil
- Will not harm environment and stops leaching of contaminants into the soil and groundwater

Cat. No.	Type	Qty.	Price
GS-10	30lb Bags	60bags/pallet	\$2,125.80



Re-Form™ Granular

- 100% recycled material - safe for the environment and employee use
- Absorb oils, solvents, lubricants, coolants, water and most non-aggressive liquids on contact
- 1:1 absorbency ratio - absorbs its own weight in oil

Cat. No.	Type	Qty.	Price
RFGRANULAR	30lb Bags	65 bags/pallet	\$620.75

Specialty Absorbent Products

A variety of spill control tools designed for specific industrial applications



Drip Pans

- Durable, low profile, polyethylene drip pans feature a wide base to prevent tipping
- Captures up to .75 gallon of liquid


Cat. No.	Type	QTY	Price
DPA24	10"x10"	24/case	\$206.57



Drain Plugs

- Keeps spills out of drainage systems
- Durable, chemical-resistant PVC
- Rinse and re-use when finished

Cat. No.	Type	QTY	Price
PLUG2	2"	1/case	\$123.18
PLUG3	3"	1/case	\$149.60
PLUG4	4"	1/case	\$166.63
PLUG6	5"	1/case	\$182.43



Slikstopper™

- Chemical-resistant, flexible PVC seals drains to prevent spill from spreading
- Resists water, oil and most aggressive fluids
- Easy soap and water cleanup for re-use


Cat. No.	Type	QTY	Price
PVC18	18"x18"	1/case	\$210.82
PVC24	24"x24"	1/case	\$305.49
PVC36	36"x36"	1/case	\$527.54
PVC42	42"x42"	1/case	\$609.01



Drum Top Covers

- Fits 55-gallon drums either with 1 or 2 bungholes
- Allwik® for all liquids or Oil Only for oil and petroleum-based liquids

Cat. #	Type	Size	Qty.	Price
DT025	Oil Only	22" dia.	25/case	\$111.46
DTA25	AllWik®	22" dia.	25/case	\$111.46



Spill Pallets

- Contain unexpected drum spills or leaks
- Comply with secondary containment regulations
- Solid construction; nestable, forklift friendly

Cat. No.	Type	Dim.	Sump Cap.	Price
SC-DP2	2 Drum pallet	26"x52"x17"	68gal.	\$335.36
SC-DP4	4 Drum pallet	52"x52"x17"	129gal.	\$500.00
SC-DPR	Ramp	33" x 70"	N/A	\$522.22
SC-SD2	2 Drum deck	26"x52"x6"	21gal.	\$215.56



Spill Berms

- Standard and lightweight available
- Self contained portable containment systems feature a one-piece design
- Requires no assembly, tools or inflation

Cat. No.	Type	Dim.	Cap.	Price
SB-1010	Standard	10'x10'x1'	748 gal.	\$3,160.00
SB-1212	Standard	12'x12'x1'	1,077 gal.	\$4,551.11
SB-SL44	Lightweight	4'x4'x8"	79 gal.	\$406.67
SB-SL46	Lightweight	4'x6'x8"	119 gal.	\$611.11



Sorbent Center

- Holds up to 38" roll and full bales
- Wall mountable or available casters
- Stackable with optional accessories

Cat. No.	Type	Quantity	Price
SC-3000	Center	1 Center	\$382.64

Spill Containment Kits

www.BradyID.com/spc

Sorbents and Spill Control

Spill Containment Kits

Spill Kits equip you with everything you need to clean up accidents when they happen. Quickly and easily clean up spills of oils, solvents, coolants and other fluids. They are ideal for fast response to critical accidents.



Economy Spill Kit™

- Ideal for small spills
- Absorbs up to 5 gallons per kit

CONTENTS: 10 pads (15" x 19"), 1 Disposal Bag, 2 SOCs (3" x 4'), Instruction Sheet, Nitrile gloves

Cat. No.	Type	Qty.	Price
SKR-PP	Re-Form	5/case	\$52.67
SKO-PP	Oil Only	5/case	\$55.79
SKA-PP	Universal Allwik	5/case	\$55.30
SKH-PP	Chemical Hazwik	5/case	\$61.84



Attack Pac™ Spill Kit

- Packed in puncture and UV resistant foil
- Absorbs up to 7 gallons per kit

CONTENTS: 15 pads (15" x 19"), 1 Disposal Bag, 3 SOCs (3" x 4'), Instruction Sheet, Nitrile gloves, Goggles

Cat. No.	Type	Qty.	Price
SKR-ATK	Re-Form	4/case	\$362.89
SKO-ATK	Oil Only	4/case	\$355.61
SKA-ATK	Universal Allwik	4/case	\$381.03
SKH-ATK	Chemical Hazwik	4/case	\$400.90



6.5 Gallon Spill Bucket

- Fast & Small response with easily accessible spill kit in a reusable bucket.
- Absorbs up to 6 gallons per kit

CONTENTS: 10 pads (15" x 19"), 3 SOCs (3" x 4') Nitrile gloves, 2 Disposal bags, Instruction Sheet

Cat. No.	Type	Qty.	Price
SKO-BKT	Oil Only	1	\$84.43
SKA-BKT	Universal Allwik	1	\$84.43
SKH-BKT	Chemical Hazwik	1	\$88.13



20 Gallon Lab Pack

- UN approved water and chemical resistant polyethylene Lab Pack container with screw top lid for small to medium response
- Absorbs up to 17 gallons per kit

CONTENTS: 12 pads (15" x 19"), Nitrile gloves, 3 SOCs (3" x 12'), 3 Disposal bags, 2 pillows (18" x 18"), Emergency Response Handbook, Goggles,

Cat. No.	Type	Qty.	Price
SKR-20	Re-Form	1	\$280.84
SKO-20	Oil Only	1	\$294.88
SKA-20	Universal Allwik	1	\$294.88
SKH-20	Chemical Hazwik	1	\$354.50



55 Gallon Drum

- Open and close this lever locked 55 gallon drum for fast response. Drum meets UN specifications. For medium spill response.
- Absorbs up to 38 gallons per kit

CONTENTS: 50 pads (15" x 19"), Nitrile gloves, 4 SOCs (3" x 12'), 5 Disposal bags, 8 pillows (18" x 18"), Emergency Response Handbook, Goggles

Cat. No.	Type	Qty.	Price
SKR-55	Re-Form	1	\$545.96
SKO-55	Oil Only	1	\$573.22
SKA-55	Universal Allwik	1	\$573.25
SKH-55	Chemical Hazwik	1	\$592.72



95 Gallon Overpack

- Tough, secure, screw topped overpack drum meets UN and DOT specifications.
- Absorbs up to 75 gallons per kit

CONTENTS: 110 pads (15" x 19"), Nitrile gloves, 12 SOCs (3" x 4'), 10 Disposal bags, 8 SOCs (3" x 12'), Emergency Response Handbook, 8 pillows (18" x 18"), Goggles

Cat. No.	Type	Qty.	Price
SKR-95	Re-Form	1	\$983.56
SKO-95	Oil Only	1	\$1,032.75
SKA-95	Universal Allwik	1	\$1,032.73
SKH-95	Chemical Hazwik	1	\$1,121.99



Mobile Spill Kaddie

- Mobile, compact emergency kit for fast spill response anywhere in the plant.
- Absorbs up to 22 gallons per kit

CONTENTS: 1 Roll (200 pads), Nitrile gloves, 5 SOCs (3" x 4'), 5 Disposal bags, 8 pillows (9" x 9"), Emergency Response Handbook, Goggles

Cat. No.	Type	Qty.	Price
SKO-K2	Oil Only	1	\$678.14
SKA-K2	Universal Allwik	1	\$694.80
SKH-K2	Chemical Hazwik	1	\$753.54



Mobile Spill Truck - Large

- Mobile spill response kit in water/chemical resistant large bin.
- Absorbs up to 126 gallons per kit

CONTENTS: 200 pads, Nitrile gloves, 24 SOCs (3" x 4'), 12 SOCs (3" x 12'), 15 Disposal bags, 8 pillows (18" x 18"), Emergency Response Handbook, Goggles

Cat. No.	Type	Qty.	Price
SKO-LT	Oil Only	1	\$1,824.31
SKA-LT	Universal Allwik	1	\$1,824.31
SKH-LT	Chemical Hazwik	1	\$1,984.78



Mobile Spill Truck - X Large

- Mobile spill response kit in water/chemical resistant large bin.
- Absorbs up to 174 gallons per kit

CONTENTS: 250 pads, 3 pair of Nitrile gloves 36 SOCs (3" x 4'), 20 SOCs (3" x 12'), 30 Disposal bags, 8 pillows (18" x 18"), Emergency Response Handbook, Goggles

Cat. No.	Type	Qty.	Price
SKO-XLT	Oil Only	1	\$2,332.85
SKA-XLT	Universal Allwik	1	\$2,332.85
SKH-XLT	Chemical Hazwik	1	\$2,527.87



Did You Know? Custom Spill Kits

Only the products you need - in the quantities you want.

Brady also offers customers the opportunity to create their own Custom Spill Kits with an assortment of Brady's most popular pads, socs, booms, pillows, safety accessories, and containers.

With no minimum requirements, these Custom Spill Kits give you the flexibility to pick only the products you need without the extra cost of items you don't want.

Choose from a wide selection of Brady's most popular Create a safer work environment and save time, money and space with a Brady SPC Custom Spill Kit.

Visit www.BradyID.com/SPC or contact Brady Customer Service for more information or to create your Custom Spill Kit.



Chemical Application Guide

www.BradyID.com/spc

Chemical Application Guide

Use the following guide to help select the right sorbent for your application.

Oil Only Polypropylene include:

- SPC Oil Sorbents
- Oil Plus
- SXT
- Oil Only SOC's & Pillows
- Trackmat
- ENV Oil Sorbents

Universal & Chemical Polypropylene include:

- MRO Plus
- UXT
- Universal Plus
- Allwik & Hazwik SOC's & Pillows
- SIR
- BSM
- BattleMat
- GP
- Cobra Coil
- High Traffic

Universal/Organic non-aggressive include:

- Re-Form
- Multiwik SOC
- Slikwik SOC
- Dri-zorb
- Rag Rug
- SW46

CHEMICAL POLYPROPYLENE	OIL ONLY POLYPROPYLENE	UNIVERSAL POLYPROPYLENE	UNIVERSAL ORGANIC
Acetaldehyde		X	X
Acetic Acid		X	
Acetic Anhydride		X	
Acetone	X	X	X
Acetyl Chloride		X	
Acrolein	X	X	
Acrylonitrile		X	X
Acrylic Acid		X	
Acrylic Emulsions		X	X
Allyl Alcohol		X	X
Aminobenzoic Acid		X	
Ammonia (Anhydrous)	X	X	X
Ammonium Hydroxide	X	X	X
Amyl Acetate	X	X	
Amyl Alcohol		X	X
Aniline		X	X
Antifreeze		X	X
Aqua Regia		X	
Aviation Fuel	X	X	X
Benzene	X	X	X
Benzoic Acid		X	
Benzonitrile		X	
Benzoyl Chloride		X	
Benzyl Alcohol		X	X
Boric Acid		X	
Brake Fluid	X	X	X
Bromine		X	
Butyl Acetate	X	X	
Butyl Alcohol	X	X	X
Butyric Acid	X	X	
Butylamine		X	X
Butyric Acid	X	X	
Calcium Hydroxide		X	
Carbolic Acid		X	
Carbon Disulfide		X	
Carbon Tetrachloride	X	X	X
Castor Oil	X	X	X
Chlorine Water		X	
Chloroacetic Acid		X	
Chlorobenzene		X	
Chloroform	X	X	X
Chromic Acid (50%)		X	
Chlorosulfonic Acid		X	
Citric Acid		X	
Clorox (Full Strength Bleach)		X	X
Corn Oil	X	X	X
Cottonseed Oil	X	X	X
Cresol	X	X	X
Cyclohexane	X	X	X
Detergents		X	X
Dichlorobenzene	X	X	
Diethylamine	X	X	
Diethyl Ether	X	X	X
Disooctyl Phthalate	X	X	X
Dinitrobenzene	X	X	
Dioxan		X	X
Ether	X	X	X
Ethyl Acetate	X	X	X
Ethyl Alcohol	X	X	X
Ethyl Benzene	X	X	
Ethyl Chloride	X	X	
Ethyl Ether	X	X	X
Ethyl Propionate	X	X	X
Ethylene Glycol		X	X
Formaldehyde		X	X
Formic Acid		X	
Fuel Oil	X	X	X
Gasoline	X	X	X
Gearbox Oil	X	X	X
Glacial Acetic Acid		X	
Glycerol		X	X

CHEMICAL POLYPROPYLENE	OIL ONLY POLYPROPYLENE	UNIVERSAL POLYPROPYLENE	UNIVERSAL ORGANIC
Heptane	X	X	X
Hexane	X	X	X
Hydrazine		X	
Hydrochloric Acid		X	
Hydrofluoric Acid		X	
Hydrogen Cyanide	X	X	
Hydrogen Peroxide		X	
Isobutyl Alcohol	X	X	X
Isobutyric Acid	X	X	
Isopropyl Acetate	X	X	X
Isopropyl Alcohol	X	X	X
Kerosene	X	X	X
Keytones	X	X	X
Linseed Oil	X	X	X
Lubricating Oil	X	X	X
Magnesium Hydroxide		X	
Methyl Alcohol	X	X	X
Methyl Chloride	X	X	
Methyl Ether	X	X	X
Methyl Ethyl Ketone	X	X	X
Methyl Propionate	X	X	X
Mineral Oil	X	X	X
Motor Oil	X	X	X
Naphthalene	X	X	X
Nitric Acid		X	
Nitrobenzene		X	
Nitrobenzoic Acid		X	
Nitrotoluene	X	X	X
Octane	X	X	X
Oleic Acid	X	X	
Olive Oil	X	X	X
Paraffin	X	X	X
Perchloroethylene	X	X	X
Petroleum Ether	X	X	X
Phenol		X	X
Phosphoric Acid		X	
Plating Solutions		X	
Potassium Hydroxide		X	
Propanol		X	X
Propionic Acid	X	X	
Propyl Alcohol	X	X	X
Propylene Glycol	X	X	X
Quinoline		X	
Resorcinol		X	
Salt Solutions (metallic)		X	X
Silicone Oil	X	X	X
Silver Nitrate		X	X
Soap Solution (concentrated)	X	X	X
Sodium Bicarbonate		X	X
Sodium Chloride		X	X
Sodium Hydroxide		X	
Sodium Hypochlorite		X	X
Sodium Nitrate		X	X
Stannic Chloride		X	
Starch		X	X
Styrene	X	X	X
Sucrose		X	X
Sulfuric Acid		X	
Synthetic Motor Oil	X	X	X
Tannic Acid		X	
Toluene	X	X	X
Transformer Oil	X	X	X
Trichloroethylene	X	X	X
Triethylene Glycol	X	X	X
Turpentine	X	X	X
Urine		X	X
Vinyl Acetate	X	X	X
Vinegar		X	X
Xylene	X	X	X

Disclaimer: The above information is provided as a guide only. No claims or warranties are expressed or implied as to the absolute accuracy of the data supplied. In all cases it is assumed chemicals in question are at ambient temperatures and pressure and are used in basic state, not in combination or mixtures. **Small test samplings by users is always recommended to ensure safe application.**

Sorbent Specifications Index

www.BradyID.com/spc

Universal

Oil Only

Chemical

Plastics

Sorbent Specifications Index

Use the following guide to quickly and easily compare sorbent specifications.

	Size	Quantity	Shipping Weight (lbs)	Absorbency Factor (gl/g)	Capacity (gal)	Static Resistant	Perforated	Absorbency Weight	Pallet Qty.
PADS									
BM100	15"x19"	100/BALE	16.5	12.5	27.5	X	X	Heavy	40
BPO100	15"x17"	100/CASE	8.5		20.5		X	Heavy	
BPO200	15"x17"	200/CASE	13.7		34.0		X	Light	
BPO500	15"x17"	100/CASE	7.0		17.0		X	Light	
BPU100	15"x17"	100/BALE	8.5		20.5		X	Heavy	
BPU200	15"x17"	200/BALE	13.7		34.0		X	Heavy	
BPU500	15"x17"	100/BALE	7.0		17.0		X	Light	
CH100	15"x19"	100/CASE	16	18	30	X	X	Medium	30
CH1212	12"x12"	200/CASE	14.5	18	30	X		Medium	24
CH1212-50	12"x12"	50/CASE	4	12.5	7.5			Medium	120
ENV100	15"x19"	100/BALE	12.5	20	33			Heavy	30
ENV200	15"x19"	200/BALE	16	23	51			Light	18
ENV300	15"x19"	100/BALE	10	20	28			Medium	36
ENV50	30"x30"	50/BALE	19	20	50			Medium	10
ENV500	15"x19"	100/BALE	8	23	16			Light	48
GP100	15"x19"	100/CASE	14.5	18	130	X		Light	18
GP100-B	15"x19"	100/BALE	12	18	30		X	Heavy	30
GP200-B	15"x19"	200/BALE	16	20	44	X		Light	18
GP300	15"x19"	100/CASE	12	12.5	52		X	Medium	36
GP500	15"x19"	100/BALE	8.2	20	22	X		Light	30-B
HAZ100-7	7.5"x34"	400/CASE	67	12.5	119			Heavy	12
MRO100	15"x19"	100/CASE	17.5	12.5	26	X	X	Heavy	30
MRO100-B	15"x19"	100/BALE	18	12.5	26		X	Heavy	30
MRO100-2	15"x19"	50/BALE	8	12.5	13.5	X	X	Heavy	36
MRO150DND	15"x19"	150/CASE	27	12.5	39	X	X	Heavy	18
MRO300	15"x19"	100/CASE	14	12.5	20.5	X	X	Medium	36
MRO50	30"x30"	50/BALE	24.5	12.5	41	X		Heavy	13
MX01000	15"x19"	100/CASE	11	23	26		X		36
MXU1000	15"x19"	100/CASE	11	24	27		X		36
OP100	15"x19"	100/CASE	17.5	12.5	26		X	Heavy	30
OP100X	15"x19"	100/BALE	17.5	12.5	26			Heavy	30
OP150DND	15"x19"	150/CASE	27	12.5	39		X	Heavy	18
OP300	15"x19"	100/CASE	14	12.5	26		X	Medium	36
OP50	30"x30"	50/BALE	17.5	12.5	41			Heavy	10
PS500	20"x20"	50/BALE	16.5	16	31.7			Heavy	2
RF100	15"x19"	100/CASE	19.0		40			Heavy	24
RF300	15"x19"	100/CASE	14.8		32			Medium	30
RF500	15"x19"	100/CASE	12.0		24			Light	36
RFP100	15"x19"	100/CASE	19.5		40		X	Heavy	24
RFP300	15"x19"	100/CASE	16.0		32		X	Medium	30
RFP500	15"x19"	100/CASE	12.7		24		X	Light	36
RFDP300	15"x19"	100/CASE	16.6		32			Medium	30
RFODP100-B	15"x19"	100/BAG	10.0	39			X	Heavy	18
RFODP100	15"x19"	100/CASE	12.0	39			X	Heavy	24
SPC100	15"x19"	100/BALE	14	18	35		X	Heavy	30
SPC200	15"x19"	200/BALE	16	18	35		X	Light	18
SPC300	15"x19"	100/BALE	11	18	30		X	Medium	36

Shipping weight and absorbency calculations are based on SPC's General Product Specifications (GPS). Some variations (within tolerances) may occur during the manufacturing process. The absorbency specification and testing method is based on the protocol of ASTM F726, using SAE20 non-detergent as the oil type, medium viscosity. Pallet quantities listed are typical and may vary depending on order size.

Sorbent Specifications Index

www.BradyID.com/spc

Sorbents and Spill Control

Universal

Oil Only

Chemical

Plastics

	Size	Quantity	Shipping Weight (lbs)	Absorbency Factor (gl/g)	Capacity (gal)	Static Resistant	Perforated	Absorbency Weight	Pallet Qty.
PADS (Continued from previous page)									
SPC500	15"x19"	100/BALE	8.2	18	20		X	Light	48
SPC50	33"x39"	50/BALE	33.5	15	74			Heavy	
10SR50	30"x30"	50/BALE						Heavy	
SR100	15 x19"	100/BALE						Heavy	
SR1825	15"x19"	25/BALE	4	15	6	X		Heavy	90
SR1850	15"x19"	50/BALE	4.5	15	9	X		Light	78
SR3625	30"x30"	25/BALE	10	15	16	X		Heavy	14
SXT100	15"x19"	100/CASE	14.5	12	19.5		X	Heavy	36
SXT200	15"x19"	200/CASE	18.6	10	31.5		X	Light	30
SXT300	15"x19"	100/CASE	12	12.5	16.5		X	Medium	
36TM30	29"x29"	30/BALE	15	9	25			Heavy	15
UN1113	12"x12"	50/BAG, 4 BAGS/CASE		16	12.5	20	X	Medium	30
UN1113-50	12"x12"	50/CASE	4	12.5	5.5		X	Medium	120
UN1719	15"x19"	100/CASE	14.5	12.5	20.5	X	X	Medium	36
UXT100	15"x19"	100/CASE	14.5	11	19	X	X	Heavy	36
UXT200	15"x19"	200/CASE	18.5	10	31.5	X	X	Light	30
UXT300	15"x19"	100/CASE	12	12.5	16.5		X	Medium	36

ROLLS

BM15	15"x150'	1/CASE	18	12.5	25	X	X	Heavy	30
BM30	30"x150'	1/CASE	34.5	12.5	52	X	X	Heavy	15
BM30X	30"x150'	1/CASE	34.5	12.5	52	X		Heavy	18
BRO150	30"x150"	1/CASE	19.5		38		X	Heavy	
BRU150	30"x150"	1/BALE	19.5		38			Heavy	
CH15P	15"x150'	1/BALE	14	12.5	20	X	X	Medium	30
CH30DP	30"x150'	1/CASE	25	12.5	40	X	X	Medium	15
ENV150	30"x150'	1/BALE	22	15	44			Medium	18
GP30	30"x150'	1/BALE	28	12.5	48	X		Heavy	18
HT15	15"x150'	1/CASE	16	12.5	23		X	Heavy	30
HT153	15"x300'	1/BALE	20	12.5	32	X	X	Medium	24
HT215	15"x300'	1/BALE						Light	
HT230	30"x300'	1/BALE					X	Light	
HT303X	30"x300'	1/BALE	40	12.5	65			Medium	12
HT350	30"x150'	1/BALE					X	Medium	
HT550	5" x 50'	1/CASE					X	Heavy	
HT30	30"x150'	1/CASE	32	12.5	47		X	Heavy	15
HT303	30"x300'	1/BALE	40	12.5	63	X	X	Medium	12
HT555	15"x150'	1/CASE	16	12.5	23	X	X	Heavy	30
MRO12P	12"x150'	1/BALE	11.5	12.5	20	X	X	Heavy	45
MRO15	15"x150'	1/CASE	17.5	12.5	24	X		Heavy	30
MRO15DP	15"x150'	1/CASE	17.5	12.5	24	X	X	Heavy	30
MRO15DPS	15"x73'	1/BALE	8	12.5	12	X	X	Heavy	80
MRO15P	15"x150'	1/CASE	17.5	12.5	24	X	X	Heavy	30
MRO24DP	24"x150'	1/BALE	22.5	12.5	39	X	X	Heavy	27
MRO30	30"x150'	1/CASE	33	12.5	49	X		Heavy	15
MRO30DP	30"x150'	1/CASE	32	12.5	49	X	X	Heavy	15
MRO30P	30"x150'	1/CASE	32	12.5	49	X	X	Heavy	15
MRO315P	15"x150'	1/CASE	14	12.5	20	X	X	Medium	30
MRO350	30"x150'	1/CASE	26.5	12.5	38	X		Medium	15
MRO350DP	30"x150'	1/CASE	26.5	12.5	38	X	X	Medium	15

Shipping weight and absorbency calculations are based on SPC's General Product Specifications (GPS). Some variations (within tolerances) may occur during the manufacturing process. The absorbency specification and testing method is based on the protocol of ASTM F726, using SAE20 non-detergent as the oil type, medium viscosity. Pallet quantities listed are typical and may vary depending on order size.

Sorbent Specifications Index

www.BradyID.com/spc

Universal

Oil Only

Chemical

Plastics

	Size	Quantity	Shipping Weight (lbs)	Absorbency Factor (gl/g)	Capacity (gal)	Static Resistant	Perforated	Absorbency Weight	Pallet Qty.
ROLLS (Continued from previous page)									
OP15	15"x150'	1/CASE	17.5	12.5	24			Heavy	30
OP15DP	15"x150'	1/CASE	17.5	12.5	24		X	Heavy	30
OP15DPS	15"x73'	1/BALE	8	12.5	12		X	Heavy	80
OP15P	15"x150'	1/CASE	17.5	12.5	24		X	Heavy	30
OP30	30"x150'	1/CASE	33	12.5	49			Heavy	15
OP30DP	30"x150'	1/CASE	32.5	12.5	49		X	Heavy	15
OP30P	30"x150'	1/CASE	32.5	12.5	49		X	Heavy	15
OP315P	15"x150'	1/CASE	14	12.5	19		X	Medium	30
OP350DP	30"x150'	1/CASE	26.5	12.5	38		X	Medium	15
OP550	15"x50'	1/CASE						Heavy	
RFP14P	14.25"x150'	1/CASE	15.5		30		X	Heavy	24
RFP28-DP	28.5"x150'	1/CASE	33.0		62		X	Heavy	12
RFP314P	14.25"x150'	1/CASE	15.5		29		X	Medium	24
RFP328-DP	28.5"x150'	1/CASE	30.5		53		X	Medium	12
RFDP314P	14.25"x150'	1/CASE	16.7		27.5			Medium	24
RFDP328-DP	28.5"x150'	1/CASE	33.3		55			Medium	12
RFOP14P	14.25"x150'	1/CASE	10.5		37		X	Heavy	24
RFOP28-DP	28.5"x150'	1/CASE	21.0		74		X	Heavy	12
SIR36150	36"x150'	1/BALE	25	12.5	45			Medium	24
SPC150	38"x144'	1/BALE	33	15	70			Heavy	18
SPC152	19"x144'	2/BALE	33	15	70			Heavy	18
SPC300	15"x19	100/bale						Medium	
SR3600	30"x150'	1/BALE	22	15	44	X		Heavy	18
SXT15P	15"x150'	1/CASE	14	12	18		X	Heavy	30
SXT30DP	30"x150'	1/CASE	26.5	12	37		X	Heavy	15
TM58	58"x80'	1/BALE	34	9	55			Heavy	9
UXT15P	15"x150'	1/CASE	14.5	11	17	X	X	Heavy	30
UXT30DP	30"x150'	1/CASE	27.5	11	35	X	X	Medium	15
UN1019	15"x150'	2/CASE	24	12.5	39	X	X	Medium	15
UN3800	30"x150'	1/CASE	27	12.5	39	X	X	Medium	15
UN75200	7.5"x200'	1/BALE		12.5	47			Heavy	12

SOCS

AW124	3"x12'	4/CASE	12	9	12	X			40
AW412	3"x4'	12/CASE	12	9	12	X			40
AW430	3"x4'	30/CASE	26	9	30	X			20
AW806	3"x8'	6/CASE	12	9	12	X			40
CC400	3"x4'	12/CASE	29	8.5	3.3				32
HAZ124	3"x12'	4/CASE	12	9	12	X			40
HAZ412	3"x4'	12/CASE	12	9	12	X			40
MS124	3"x12'	4/CASE	12.0		12				42
MS412	3"x4'	12/CASE	12.0		12				42
MS50	3"x4'	40/CASE	43	7	40				15
MS806	3"x8'	6/CASE	12.0		12				42
OIL124	3"x12'	4/CASE	11	9	12				40
OIL412	3"x4'	12/CASE	11	9	12				40
OIL430	3"x4'	30/CASE	30	9	28				20
OIL806	3"x8'	6/CASE	11	9	12				40
RFO412	3"x4'	12/CASE	10.5		15				42
SW46	3"x42"	40/CASE	45-50	3	20				16

Shipping weight and absorbency calculations are based on SPC's General Product Specifications (GPS). Some variations (within tolerances) may occur during the manufacturing process. The absorbency specification and testing method is based on the protocol of ASTM F726, using SAE20 non-detergent as the oil type, medium viscosity. Pallet quantities listed are typical and may vary depending on order size.

Sorbents

www.BradyID.com/spc

Sorbents and Spill Control

Universal

Oil Only

Chemical

Plastics

	Size	Quantity	Shipping Weight (lbs)	Absorbency Factor (gl/g)	Capacity (gal)	Static Resistant	Perforated	Absorbency Weight	Pallet Qty.
RUGS									
BSM100	36"x100'	1/BALE	24	8	25	X		Medium	40
BSM300	36"x300'	1/BALE	67	8	74	X		Medium	12
BSM3650	36"x50'	1/CASE	12	8	12	X		Medium	40
RAG1818	18"x18"	10	18	9	4			Heavy	18
RAG24150	24"X150	1/BALE	52	9	37			Heavy	
RAG36150	36"x150'	1/BALE	47	9	55	X		Heavy	10
SIR36	36"x300'	1/BALE	50	8.5	59	X		Medium	12
SIR72	72"x150'	1/BALE	50	8.5	59	X		Medium	12

LOOSE GRANULAR

DZ100	DRI-ZORB (CORN COB)	1 BAG	40	1.5	8.5				50
RFGRANULAR	30 lbs	65/PALLET							65
GS-10	OIL GATOR	1 BAG	30	2 to 6					60

BOOMS, DRAG NETS, PILLOWS & SWEEPS

AW1818	18"x18"	16/CASE	19	12.5	28	X			20
AW1818-2	18"x18"	8/CASE	9.5	12.5	14	X			40
AW99	9"x9"	32/CASE	10	12.5	14	X			40
ENV810	8"x10'	4/BALE	38	13	65				10
ENV510	5"x10'	4/BALE	19	13	32				
HAZ1818	18"x18"	16/CASE	9.5	12.5	14	X			20
HAZ1818-2	18"x18"	8/CASE	9.5	12.5	14	X			40
HAZ99	9"x9"	32/CASE	14	12.5	10	X			40
OIL1818	18"x18"	16/CASE	19	12.5	28				20
OIL1818-2	18"x18"	8/CASE	9.5	12.5	14	X			40
OIL99	9"x9"	32/CASE	10	12.5	14				40
ODN08	30 HALF-POUND UNITS	1/BALE	16	15	15				24
RF0510	5"x10'	4/BALE							
RF0810	8"x10'	4/BALE							
SPC10	14"x25"	10/BALE	30	12.5	52				10
SPC318	3"x18" Boom	10/CASE	10	12.5	14				
SPC510	5"x10'	4/BALE	19	13	32				16
SPC518	5"x18" Boom	10/CASE	8	12.5	12				
SPC5510	5"x10'	2/BALE	38	12	61				12
SPC810	8"x10'	4/BALE	40	13	71				10
SPC818	8"x18"	10/BALE	17	12.5	28				16
SPC1900	19"X100'	1/BALE	13	15	26				36

SPECIALTY SORBENT PRODUCTS

DPA24	10"x10"	24/CASE							
DTA25	22" DIAMETER	25/CASE	6	12.5	6	X		Medium	48
DT025	22" DIAMETER	25/CASE	6	12.5	6			Medium	48
PLUG2	2" Plug	1/CASE							
PLUG3	3" Plug	1/CASE							
PLUG4	4" Plug	1/CASE							
PLUG6	5" Plug	1/CASE							
PVC18	18"x18"	1/CASE							
PVC24	24"x24"	1/CASE							
PVC36	36"x36"	1/CASE							

Shipping weight and absorbency calculations are based on SPC's General Product Specifications (GPS). Some variations (within tolerances) may occur during the manufacturing process. The absorbency specification and testing method is based on the protocol of ASTM F726, using SAE20 non-detergent as the oil type, medium viscosity. Pallet quantities listed are typical and may vary depending on order size.

- Universal
- Oil Only
- Chemical
- Plastics

	Size	Quantity	Shipping Weight (lbs)	Absorbency Factor (gl/g)	Capacity (gal)	Static Resistant	Perforated	Absorbency Weight	Pallet Qty.
--	------	----------	-----------------------	--------------------------	----------------	------------------	------------	-------------------	-------------

DRAIN GUARDS

DGUARDS9	36" X 48" X 18"	1/CASE							
DGUARDS14	36" X 48" X 18"	1/CASE (w/ X-Tex filter strips)							
DGUARDS9	36" X 48" X 18"	10/CASE							
DGUARDS14"	36" X 48" X 18"	10/CASE (w/ X-Tex filter strips)							

SPILL KITS

SKA-20	21" Dia. X 18"H	1/EACH	27	N/A	15				20
SKA-55	24" Dia. X 37"H	1/EACH	57	N/A	38				8
SKA-95	31.5" Dia. X 35"H	1/EACH	107	N/A	75				4
SKA-ATK	20.5"L X 20.5"W X 18.25"H	4/CASE	36.5	N/A	7				24
SKA-BKT	14" Dia. X 18"H	1/EACH	9	N/A	9				20
SKA-K2	18"L X 17"W X 39"H	1/EACH	42	N/A	22				12
SKA-LT	47"L X 34"W X 43"H	1/EACH	164	N/A	126				1
SKA-PP	20"L X 16"W X 4"H	5/CASE	24	N/A	5				50
SKA-XLT	57.5"L X 40.5"W X 47"H	1/EACH	221	N/A	174				1
SKH-20	21" Dia. X 18"H	1/EACH	26	N/A	15				20
SKH-55	24" Dia. X 37"H	1/EACH	52	N/A	38				8
SKH-95	31.5" Dia. X 35"H	1/EACH	104	N/A	75				4
SKH-ATK	20.5"L X 20.5"W X 18.25"H	4/CASE	25	N/A	7				24
SKH-BKT	14" Dia. X 18"H	1/EACH	8	N/A	9				20
SKH-K2	18"L X 17"W X 39"H	1/EACH	42	N/A	22				12
SKH-LT	47"L X 34"W X 43"H	1/EACH	158	N/A	115				1
SKH-PP	20"L X 16"W X 4"H	5/CASE	24	N/A	5				50
SKH-XLT	57.5"L X 40.5"W X 47"H	1/EACH	221	N/A	160				1
SKO-20	21" Dia. X 18"H	1/EACH	20	N/A	15				20
SKO-55	24" Dia. X 37"H	1/EACH	56	N/A	38				8
SKO-95	31.5" Dia. X 35"H	1/EACH	107	N/A	75				4
SKO-ATK	20.5"L X 20.5"W X 18.25"H	4/CASE	23	N/A	7				24
SKO-BKT	14" Dia. X 18"H	1/EACH	9	N/A	9				20
SKO-K2	18"L X 17"W X 39"H	1/EACH	42	N/A	22				12
SKO-LT	47"L X 34"W X 43"H	1/EACH	185	N/A	126				1
SKO-PP	20"L X 16"W X 4"H	5/CASE	24	N/A	5				50
SKO-XLT	57.5"L X 40.5"W X 47"H	1/EACH	221	N/A	174				1
SKR-PP	20"L X 16"W X 4"H	5/CASE			5				
SKR-20	21" Dia. X 18"H	1/EACH			15				
SKR-55	24" Dia. X 37"H	1/EACH			38				
SKR-95	31.5" Dia. X 35"H	1/EACH			75				
SKR-ATK	20.5"L X 20.5"W X 18.25"H	4/CASE			7				
SKR-BKT	14" Dia. X 18"H	1/EACH			6				

SORBENT CENTERS & SPILL CONTAINMENT

SB-1010	10'x10'x1' Standard	748 gal.							
SB-1212	12'x12'x1' Standard	1,077 gal.							
SB-SL44	4'x4'x8" Lightweight	79 gal.							
SB-SL46	4'x6'x8" Lightweight	119 gal.							
SC-3000	50"L X 26"W X 7.75"H	1/EACH	50	N/A	N/A				
SC-DP2	26"W X 52"L X 17"H	1/EACH	46.5	N/A	68.7				
SC-DP4	52"W X 52"L X 17"H	1/EACH	89	N/A	128.9				
SC-DPR	32.5"W X 70"L	1/EACH	47.5	N/A	N/A				
SC-SD2	26"W X 52"L X 6"H	1/EACH	31	N/A	21.2				

Shipping weight and absorbency calculations are based on SPC's General Product Specifications (GPS). Some variations (within tolerances) may occur during the manufacturing process. The absorbency specification and testing method is based on the protocol of ASTM F726, using SAE20 non-detergent as the oil type, medium viscosity. Pallet quantities listed are typical and may vary depending on order size.

Lockout/Tagout Overview

www.BradyID.com/lockouttagout

Why Lockout/Tagout?

- OSHA Focus #1 most cited violation for general industry
- Best Practice - Being adopted across industries & geographies
- Saves Lives - Prevents an estimated 120 fatalities & 50,000 injuries annually
- Significantly Cuts Costs - Both lost time and insurance costs
- Improves Productivity - Minimizes equipment downtime



5-Steps To An Effective Lockout Program

Step 1

Develop and document your energy control policy/program



Step 2

Create and post written, equipment-specific lockout procedures



Step 3

Identify and mark all energy control points



Step 4

Train your employees, communicate and conduct periodic inspections



Step 5

Equip your employees with the proper lockout tools and warning devices



Lockout/Tagout Overview

www.BradyID.com/lockouttagout

OSHA 29 CFR §1910.147 The control of hazardous energy

(Lockout/Tagout).

Scope, application and purpose

- (1) Scope. (i) This standard covers the servicing and maintenance of machines and equipment in which the unexpected energization or start up of the machines or equipment, or release of stored energy could cause injury to employees. This standard establishes minimum performance requirements for the control of such hazardous energy.
- (2) Application. (i) This standard applies to the control of energy during servicing and / or maintenance of machines and equipment.
- (3) Purpose. (i) This section requires employers to establish a program and utilize procedures for affixing appropriate lockout devices or tagout devices to energy isolating devices, and to otherwise disable machines or equipment to prevent unexpected energization, start-up or release of stored energy in order to prevent injury to employees.



1910.147(c) OSHA Energy Control Policy;

Synopsis of Requirements

An energy control policy must be documented and at a minimum should cover the following aspects of the program:

- Purpose and scope of the program
- Personnel authorized to perform LOTO
- Enforcement policy
- Training methods
- Group lockout procedures
- Shift transfer procedures
- Lock removal procedures
- Method for auditing & updating procedures
- Coordination with outside contractors

1910.147(c)(4) Energy Control Procedures;

Synopsis of Requirements

- Procedures must be documented and must identify the equipment covered.
- A separate procedure must be created for each piece of equipment to be locked out. There are exceptions where multiple machines may be grouped under a single procedure.
- The procedure must include specific steps for shutting down, isolating, blocking and securing equipment to control hazardous energy.
- Specific steps for the placement, removal and transfer of lockout/tagout devices should also be included.
- The employer shall conduct and certify periodic inspections at least annually.



1910.147(c)(5) OSHA Lockout Device Requirements

LOCKOUT DEVICES MUST:

- Be provided by the employer.
- Be standardized by size, shape or color.
- Be distinguishable from locks used for other purposes. Lockout locks should only be used for lockout!
- Identify the individual who applied the lock (both tags and lock labels are acceptable for this purpose).
- Be durable.
- Be strong enough to prevent removal except by using excessive force.
- Remain under the exclusive control of the individual who attached them.

1910.147(c)(5)(ii)(B) *Standardized.*

Lockout and tagout devices shall be standardized within the facility in at least one of the following criteria: Color; shape; or size; and additionally, in the case of tagout devices, print and format shall be standardized.

1910.147(c)(5)(ii)(A) *Durable.*

Lockout and tagout devices shall be capable of withstanding the environment to which they are exposed for the maximum period of time that exposure is expected.

Personal Lockout Kits

www.BradyID.com/lockouttagout

Personal Lockout Kits

Personal lockout kits come equipped with keyed-alike padlocks, allowing all the locks in a kit to be opened with a single key. This simplifies key management and ensures that employees can quickly and easily find the right key. For kits containing padlocks that are keyed different (each padlock has its own unique key), see the standard lockout kits on the following pages. Or select a personal lockout kit without padlocks, and purchase the padlocks separately (see page 198-121 for padlocks sold separately.)



Personal Padlock Pouch

- Compact kit that contains padlocks, tags and hasps.
- Components:
 - 2 - 1" Group Lockout Hasps (65375)
 - 2 - Heavy Duty Lockout Tags (65520) w/ Nylon Cable Ties
 - 2 - Keyed-alike Safety Padlocks (99552) or Steel Padlocks (99500)
 - 1 - Lockout Belt Pouch (51172)

Catalog No.	Description	Price Each
105969	Padlock kit w/ Keyed-Alike Safety Padlocks	\$79.32
105970	Padlock kit w/ Keyed-Alike Steel Padlocks	\$81.18



Personal Breaker Lockout Pouch

- Pouch contains 1 each of our most popular circuit breaker lockouts
- Covers 120v/277v and 480/600v breakers in single- and multi-pole configurations.
- Components:
 - 1 - 120/277V Clamp-On Breaker Lockout w/cleat (65396)
 - 1 - 480/600V Clamp-On Breaker Lockout w/cleat (65397)
 - 1 - Universal Multipole Breaker Lockout (66321)
 - 2 - 1" Group Lockout Hasps (65375)
 - 2 - Heavy Duty Lockout Tags (65520) w/ Nylon Cable Ties
 - 1 - Lockout Belt Pouch (51172)

Catalog No.	Description	Price Each
105966	Personal Breaker Lockout Pouch (Kit)	\$71.47
105967	Kit w/ 2 Keyed-Alike Safety Padlocks	\$107.03
105968	Kit w/ 2 Keyed-Alike Steel Padlocks	\$111.01



For more information on breaker lockouts see page 214

Personal Breaker Lockout Kit

- Toolbox contains 2 each of our most popular breaker lockouts
- Covers 120v/277v and 480/600v breakers in single- and multi-pole configurations.
- Components:
 - 2 - 120/277V Clamp-On Breaker Lockouts w/ Cleats (65396)
 - 2 - 480/600V Clamp-On Breaker Lockouts w/ Cleats (65397)
 - 2 - Universal Multipole Breaker Lockouts (66321)
 - 3 - 1" Red Lockout Hasps (65375)
 - 3 - Heavy Duty Lockout Tags (65520) w/ Nylon Cable Ties
 - 1 - Small Lockout Toolbox (105905)

Catalog No.	Description	Price Each
105963	Personal Breaker Lockout Kit	\$107.23
105964	Kit w/ 3 Keyed-Alike Safety Padlocks	\$160.86
105965	Kit w/ 3 Keyed-Alike Steel Padlocks	\$166.83

Personal Basic Lockout Kit

- Contains the basic devices needed to lockout common breakers, valves and plugs
- Components:
 - 1 - 1/2" - 2 1/2" Small Ball Valve Lockout (BS07A)
 - 1 - 1" - 2 1/2" Gate Valve Lockout (65560)
 - 1 - 120/277V Clamp-On Breaker Lockout w/ Cleat (65396)
 - 1 - Universal Multipole Breaker Lockout (66321)
 - 1 - Small 110V Electrical Plug Lockout (65674)
 - 2 - 1" Lockout Hasps (65375)
 - 2 - Heavy Duty Lockout Tags (65520) w/ Nylon Cable Ties
 - 1 - Small Lockout Toolbox (105905)



Catalog No.	Description	Price Each
104794	Personal Basic Lockout Kit	\$107.23
104795	Kit w/ 2 Keyed-alike Safety Padlocks	\$138.22
104796	Kit w/ 2 Keyed-alike Steel Padlocks	\$142.99

Personal Electrical Lockout Kit

- Provides lockouts for use on most circuit breakers, electrical plugs and disconnect switches.
- Components:
 - 1 - Mini Cable Lockout (50940)
 - 1 - 3-in-1 Electrical Plug Lockout (PLO23)
 - 2 - 120/277V Clamp-On Breaker Lockouts w/ Cleats (65396)
 - 1 - 480/600V Clamp-On Breaker Lockout w/ Cleat (65397)
 - 2 - Universal Multipole Breaker Lockout (66321)
 - 1 - Oversized Breaker Lockout (65329)
 - 3 - 1" Group Lockout Hasps (65375)
 - 3 - Heavy Duty Lockout Tags (65520) w/ Nylon Cable Ties
 - 1 - Medium Lockout Toolbox (105906)

Includes Mini Cable Lockout, see page 211 for details.



Catalog No.	Description	Price Each
105960	Personal Electrical Lockout Kit	\$178.76
105961	Kit w/3 Keyed-alike Safety Padlocks	\$229.62
105962	Kit w/3 Keyed-alike Steel Padlocks	\$233.04

Personal Valve Lockout Kit

- Contains devices for locking out a wide range of gate and ball valves
- Components:
 - 1 - 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
 - 1 - 1" - 2 1/2" Gate Valve Lockout (65560)
 - 1 - 1/2" - 2 1/2" Small Ball Valve Lockouts (BS07A)
 - 1 - All Purpose Cable Lockout (50943)
 - 3 - 1" Group Lockout Hasps (65375)
 - 3 - Heavy Duty Lockout Tags (65520) w/ Nylon Cable Ties
 - 1 - Medium Lockout Toolbox (105906)

Looking for a Plug Valve Lockout? See page 212 for details.



Catalog No.	Description	Price Each
105957	Personal Valve Lockout Kit	\$202.59
105958	Kit w/ 3 Keyed-Alike Safety Padlocks	\$247.88
105959	Kit w/ 3 Keyed-Alike Steel Padlocks	\$253.85

Personal Valve & Electrical Lockout Kit

- Provides everything you need to lockout breakers, plugs and valves of various types and sizes
- Components:
 - 1 - All Purpose Cable Lockout (50943)
 - 1 - 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
 - 1 - Plug Valve Lockout for stem dia up to 7/8" (113231)
 - 1 - Plug Valve Lockout for stem dia 9/32" - 13/8" (113232)
 - 1 - 1/2" - 2 1/2" Small Ball Valve Lockout (BS07A)
 - 1 - 3-in-1 Electrical Plug Lockout (PLO23)
 - 2 - 120/277V Clamp-On Breaker Lockouts w/ Cleats (65396)
 - 1 - 480/600V Clamp-On Breaker Lockout w/ Cleat (65397)
 - 2 - Universal Multipole Breaker Lockouts (66321)
 - 3 - 1" Group Lockout Hasps (65375)
 - 3 - Heavy Duty Lockout Tags (65520) w/ Nylon Cable Ties
 - 1 - Medium Lockout Toolbox (105906)

Includes Plug Valve Lockouts pictured on page 212.



Catalog No.	Description	Price Each
105954	Personal Valve & Electrical Kit	\$262.66
105955	Kit w/ 3 Keyed-Alike Safety Padlocks	\$309.67
105956	Kit w/ 3 Keyed-Alike Steel Padlocks	\$317.68

Standard Lockout Kits

www.BradyID.com/lockouttagout

Standard Lockout Kits

The kits shown on pages 182-185 can be purchased with or without padlocks and tags. The padlocks included in these kits are keyed differently (each lock has its own unique key). For kits with keyed-alike padlocks (all locks can be opened with the same key), see the personal lockout kits on pages 180-181.



Portable Padlock Pouch

- Portable kit with padlocks, tags and hasps
- Components:
 - 2 - Choose between keyed-different safety padlocks (99552) or steel padlocks (99500)
 - 2 - Heavy Duty Lockout Tags (65520) w/ Nylon Cable Ties
 - 1 - 1" Group Lockout Hasp (65375)
 - 1 - 1.5" Group Lockout Hasp (65376)
 - 1 - Lockout Belt Pouch (51172)

Catalog No.	Description	Price Each
99290	Kit w/2 Safety Padlocks	\$75.46
99292	Kit w/2 Steel Padlocks	\$74.33



Breaker Lockout Sampler Pouch

- Contains one each of our most popular breaker lockouts
- Components:
 - 1 - 120V Snap-On Breaker Lockout (65387)
 - 1 - 120/277V Clamp-On Breaker Lockout w/cleat (65396)
 - 1 - 480/600V Clamp-On Breaker Lockout w/cleat (65397)
 - 1 - Universal Multi-Pole Breaker Lockout (66321)
 - 1 - Oversized Breaker Lockout (65329)
 - 1 - Lockout Belt Pouch (51172)
- Padlock Options:
 - Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
 - Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog No.	Description	Price Each
99293	Breaker Lockout Sampler Toolbox (Kit)	\$75.21
99296	Kit w/2 Safety Padlocks & 2 Tags	\$106.47
99297	Kit w/2 Steel Padlocks & 2 Tags	\$105.30



120/277V Breaker Lockout Pouch

- Contains all the devices you need to lockout most 120/277V breakers
- Components:
 - 2 - 120V Snap-On Breaker Lockouts (65387)
 - 2 - 120/277V Clamp-On Breaker Lockout w/ Cleats (65396)
 - 2 - Universal Multi-Pole Breaker Lockout w/ Cleats (66321)
 - 1 - Lockout Belt Pouch (51172)
- Padlock Options:
 - Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
 - Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog No.	Description	Price Each
99300	120/277V Breaker Lockout Pouch (Kit)	\$78.42
99302	Kit w/2 Safety Padlocks & 2 Tags	\$109.67
99303	Kit w/2 Steel Padlocks & 2 Tags	\$108.50

Standard Lockout Kits

www.BradyID.com/lockouttagout

Breaker Lockout Toolbox

- Everything you need to lockout most circuit breakers
- Includes Mini Cable Lockout (see page 159 for details)
- Components:
 - 1 - Mini Cable Lockout (50940)
 - 2 - 120V Snap-On Breaker Lockout (65387)
 - 2 - 120/277V Clamp-On Breaker Lockouts w/cleats (65396)
 - 2 - 480/600V Clamp-On Breaker Lockouts w/cleats (65397)
 - 1 - Universal Multi-Pole Breaker Lockout (66321)
 - 1 - Oversized Breaker Lockout (65329)
 - 1 - Lockout Toolbox (65290)
- Padlock Options:
 - Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
 - Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties



Catalog No.	Description	Price Each
99305	Breaker Lockout Toolbox (Kit)	\$143.64
99307	Kit w/2 Safety Padlocks & 2 Tags	\$174.88
99308	Kit w/2 Steel Padlocks & 2 Tags	\$173.71

Electrical Lockout Toolbox

- All the basics for locking out breakers, electrical plugs, wall switches and fuses
- Includes Mini Cable Lockout (see page 205 for details)
- Components:
 - 1 - Mini Cable Lockout (50940)
 - 2 - 120V Snap-On Breaker Lockouts (65387)
 - 2 - 120/277V Clamp-On Breaker Lockouts w/cleats (65396)
 - 2 - 480/600V Clamp-On Breaker Lockouts w/cleats (65397)
 - 2 - Universal Multi-Pole Breaker Lockouts (66321)
 - 2 - Cleats for 120/277V Clamp-On Lockouts (65404)
 - 2 - Cleats for 480/600V Clamp-On Lockouts (65406)
 - 1 - Oversized Breaker Lockout (65329)
 - 1 - 3-in-1 Electrical Plug Lockout (PLO23)
 - 1 - Wall Switch Lockout (65392)
 - 1 - Small Fuse Blockout (65690)
 - 1 - Large Fuse Blockout (65691)
 - 1 - Extra-Large Lockout Toolbox (LKP-TKLBOX)
 - 1 - Red Belt Pouch (51172)
- Padlock Options:
 - Choose between two keyed-different safety padlocks (99552) or steel padlock (99500).
 - Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties



Catalog No.	Description	Price Each
99310	Electrical Lockout Toolbox (Kit)	\$214.38
99312	Kit w/2 Safety Padlocks & 2 Tags	\$244.32
99313	Kit w/2 Steel Padlocks & 2 Tags	\$243.19

Lockout Kits

www.BradyID.com/lockouttagout



Valve Lockout Pouch

- Economical kit for locking out gate, ball and plug valves
- Components:
 - 1 - 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
 - 2 - 1/2" - 2 1/2" Small Ball Valve Lockout (BS07A)
 - 1 - Large Lockout Pouch (50979)

Catalog No.	Description	Price Each
99679	Valve Lockout Pouch (Kit)	\$126.98
99680	Kit w/2 Safety Padlocks & 2 Tags	\$157.78
99681	Kit w/2 Steel Padlocks & 2 Tags	\$156.28

- 1 - Plug Valve Lockout for stem dia up to 7/8" (113231)
- 1 - Plug Valve Lockout for stem dia 29/32" - 13/8 (113232)

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties



Gate Valve Lockout Pouch

- Lockout virtually any type and size of gate valve with just two versatile lockouts
- Components:
 - 1 - 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
 - 1 - All Purpose Cable Lockout w/ 8" sheathed cable (50943)

Catalog No.	Description	Price Each
101416	Gate Valve Lockout Pouch (Kit)	\$115.90
102692	Kit w/2 Safety Padlocks & 2 Tags	\$142.99
102693	Kit w/2 Steel Padlocks & 2 Tags	\$140.60

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties



Gate Valve Lockout Satchel

- Components:
 - 1 - 1" - 2 1/2" Gate Valve Lockout (65560)
 - 1 - 2 1/2" - 5" Gate Valve Lockout (65561)
 - 1 - 5" - 6 1/2" Gate Valve Lockout (65562)
 - 1 - 6 1/2" - 10" Gate Valve Lockout (65563)
 - 1 - 10" - 13" Gate Valve Lockout (65564)
 - 1 - Lockout Satchel (51173)

Catalog No.	Description	Price Each
99676	Gate Valve Lockout Satchel (Kit)	\$253.53
99677	Kit w/2 Safety Padlocks & 2 Tags	\$283.15
99678	Kit w/2 Steel Padlocks & 2 Tags	\$283.03

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties



Valve Lockout Toolbox

- Everything you need to lock out gate, ball, butterfly and other valves
- Components:
 - 1 - Small Univ. Valve Lockout w/ Blocking Arm (50924 and 65402)
 - 1 - All Purpose Cable Lockout w/ 8' Sheathed Cable (50943)
 - 1 - 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
 - 1 - 1/4" - 1" Ball Valve Lockout (65666)
 - 1 - 1" - 2 1/2" Gate Valve Lockout (65560)
 - 1 - Extra-Large Lockout Toolbox (LKP-TKLBOX)

Catalog No.	Description	Price Each
99320	Gate Valve Lockout Toolbox (Kit)	\$214.81
99321	Kit w/2 Safety Padlocks & 2 Tags	\$246.06
99324	Kit w/2 Steel Padlocks & 2 Tags	\$244.89

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties

Combination Lockout Satchel

- Everything you need to lock out the most common mechanical and electrical control points, with extra valve lockout devices
- Components:
 - 1 - Large Univ. Valve Lockout w/ Blocking Arm (50899 and 65403)
 - 1 - All Purpose Cable Lockout w/ 8' Sheathed Cable (50943)
 - 1 - 1/4" - 1" Ball Valve Lockout (65666)
 - 1 - 1" - 2 1/2" Gate Valve Lockout (65560)
 - 1 - 2 1/2" - 5" Gate Valve Lockout (65561)
 - 1 - 5" - 6 1/2" Gate Valve Lockout (65562)
 - 1 - 120V Snap-On Breaker Lockout (65387)
 - 1 - 120/277V Clamp-On Breaker Lockout w/ Cleat (65396)

Catalog No.	Description	Price Each
99686	Combination Lockout Satchel (Kit)	\$322.51
99687	Kit w/2 Safety Padlocks & 2 Tags	\$352.12
99688	Kit w/2 Steel Padlocks & 2 Tags	\$351.02

- 1 - 480/600V Clamp-On Breaker Lockout w/cleat (65397)
- 1 - Universal Multi-Pole Breaker Lockout (66321)
- 1 - 110V Electrical Plug Lockout (65674)
- 1 - Wall Switch Lockout (65392)
- 1 - Lockout Satchel (51173)

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or two steel padlocks (99500).
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties



Combination Lockout Toolbox

- All the basics for lockout out gate and ball valves, breakers, switches and plugs
- Components:
 - 1 - 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
 - 1 - 1/4" - 1" Ball Valve Lockout (65666)
 - 1 - 1 1/4" - 3" Ball Valve Lockout (65669)
 - 1 - 120V Snap-On Breaker Lockout (65387)
 - 1 - 120/277V Clamp-On Breaker Lockout w/cleat (65396)
 - 1 - 480/600V Clamp-On Breaker Lockout w/cleat (65397)

Catalog No.	Description	Price Each
99682	Combination Lockout Toolbox (Kit)	\$216.98
99684	Kit w/2 Safety Padlocks & 2 Tags	\$246.57
99685	Kit w/2 Steel Padlocks & 2 Tags	\$245.46

- 1 - Universal Multi-Pole Breaker Lockout (66321)
- 1 - 110V Electrical Plug Lockout (65674)
- 1 - Wall Switch Lockouts (65392)
- 1 - Lockout Belt Pouch (51172)
- 1 - Extra-Large Lockout Toolbox (LKP-TKLBOX)

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties



Combination Lockout Duffel

- Everything you need to lock out the most common mechanical and electrical control points, with extra electrical lockout devices
- Components:
 - 1 - Mini Cable Lockout (50940)
 - 1 - 120V Snap-On Breaker Lockout (65387)
 - 1 - 120/277V Clamp-On Breaker Lockout (65396)
 - 1 - 480/600V Clamp-On Breaker Lockout (65397)
 - 1 - Universal Multi-Pole Breaker Lockout (66321)
 - 1 - Oversized Breaker Lockout (65329)
 - 1 - 3-in-1 Electrical Plug Lockout (PLO23)
 - 1 - Wall Switch Lockout (65392)

Catalog No.	Description	Price Each
99689	Combination Lockout Duffel (Kit)	\$388.94
99690	Kit w/2 Safety Padlocks & 2 Tags	\$417.42
99691	Kit w/2 Steel Padlocks & 2 Tags	\$416.33

- 1 - Plug Valve Lockout for stem dia up to 7/8" (113231)
- 1 - Plug Valve Lockout for stem dia 29/32"- 13/8 (113232)
- 1 - 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
- 1 - 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 - 1/4" - 1" Ball Valve Lockout (65666)
- 1 - Large Univ. Valve Lockout w/ Blocking Arm (50899 and 65403)
- 1 - Lockout Belt Pouch (51172)
- 1 - Lockout Duffel Bag (99162)

Padlock Options:

- Choose between two keyed-different safety padlocks (99552) or steel padlocks (99500).
- Padlocks come with two heavy duty, re-usable lockout tags (65520) and nylon cable ties



Lockout/Tagout

www.BradyID.com/lockouttagout

Customize It

Create your own custom lockout kits by picking one of the storage/carrying cases below and filling it with the lockout devices you need!



Lockout Belt Pouch

- Made of heavy duty nylon with loops for hanging on a belt
- Dimensions: 4³/₄"h x 7¹/₂"w x 2"d

Catalog No.	Description	Price Each
51172	Lockout Belt Pouch	\$30.78



Large Lockout Pouch

- Made of nylon with attachment loop on back
- Dimensions: 8"h x 7"w x 3"d

Catalog No.	Description	Price Each
50979	Large Lockout Pouch	\$36.95



Lockout Bag

- Made of rugged canvas with drawstring
- Capable of being locked closed
- Dimensions: 9³/₄"h x 18"l

Catalog No.	Description	Price Each
65780	Lockout Security Bag	\$50.07



Lockout Satchel

- Made of 1000 Denier Red Cordura Nylon with 39" shoulder strap
- Includes latchable front pocket and two side mesh holders
- Dimensions: 14"h x 4"w x 15"d

Catalog No.	Description	Price Each
51173	Lockout Satchel	\$73.96



Extra-Large Lockout Toolbox

Catalog No.	Description	Price Each
LKX-TKLBO	Lockout Toolbox	\$38.98

Lockout Duffel Bag

- Made of 600 denier polyester with 39" removable shoulder strap and 8 inside pockets
- Dimensions: 10"h x 16 1/2"w x 8 1/2"d

Catalog No.	Description	Price Each
99162	Lockout Duffel Bag	\$86.30



Lockout Toolboxes

- Made of rugged polypropylene with nickel-plated steel clasps
- Two handy storage pockets built into lid
- Comes with removable tray for organizing contents

Catalog No.	Dimensions(H x W x D)	Description	Price Each
105905	7.1" x 14" x 5.5"	Small Toolbox	\$23.79
105906	7.8" x 16.2" x 7.3"	Medium Toolbox	\$29.74



PRINZING Metal Lockout Cabinet

- All metal, yellow powder-coated cabinet comes with one adjustable shelf (extra shelves available)
- Capable of being locked closed
- Can also be easily wall mounted using predrilled holes in back
- Lockout safety tips printed on inside door
- Dimensions: 16"h x 14"w x 6"d

Catalog No.	Description	Price Each
LC252M	Metal Lockout Cabinet	\$190.73
LC254M	Extra Shelf	\$11.86



Ready Access Lockout Station

- Made of thermformed polypropylene for rugged durability
- Semi-transparent hinged cover with locking mechanism protects contents from harsh environments and prevents unauthorized access
- Slots in back for wall mounting
- Attachable carrying handle facilitates easy portability
- 4 Small Detachable hanging hooks
- Storage compartment (4.25"H x 16"W x 5.12"D)
- Dimensions: 17" H x 17"W x 6.75"D

Catalog No.	Description	Price Each
105942	Ready Access Lockout Station (unfilled)	\$106.83



Closed

Ready Access Storage Stations

www.BradyID.com/lockouttagout

Ready Access Storage Stations

Brady's new Ready Access storage stations ensure that lockout devices remain easily accessible and ready for use whenever needed. These compact stations are made of rugged, rustproof polypropylene and come with an attachable handle for easy portability. The stations can also be permanently wall-mounted out near the point of need, allowing employees to grab the tools they need without wasted search and retrieval time. The lockable cover guards against theft and unauthorized usage, and protects the contents from exposure to harsh industrial environments. Your lockout devices stay clean and secure, ready for use whenever and wherever needed.



Ready Access Padlock Station

- Holds up to 10 padlocks, 6 hasps and 10 tags
- Made of thermformed polypropylene for rugged durability
- Semi-transparent hinged cover with locking mechanism protects contents from harsh environments and prevents unauthorized access
- Slots in back for wall mounting
- Attachable carrying handle facilitates easy portability
- Space-saving design delivers footprint half the size of competitors
- Dimensions: 17"H x 13.25"W x 2.5"D

Ready Access Padlock Station - with 5 Padlocks

Components:

- 1 Ready Access Padlock Station (105932)
- 5 Keyed-different safety padlocks (99552) or steel padlocks (99500)
- 5 Heavy Duty, re-usable lockout tags (65520) w/ nylon cable tie
- 2 1" Group Lockout Hasps (65375)
- 2 1.5" Group Lockout Hasps (65376)

Ready Access Padlock Station - with 10 Padlocks

Components:

- 1 ReadyAccess Padlock Station (105932)
- 10 Keyed-different safety padlocks (99552) or steel padlocks (99500)
- 10 Heavy duty, re-usable lockout tags (65520) w/ nylon cable ties
- 3 1" Group Lockout Hasps (65375)
- 3 1.5" Group Lockout Hasps (65376)

Catalog No.	Description	Price Each
105928	Padlock Station w/ 5 Safety Padlocks	\$185.22
105929	Padlock Station w/ 5 Steel Padlocks	\$176.40
105930	Padlock Station w/ 10 Safety Padlocks	\$297.68
105931	Padlock Station w/ 10 Steel Padlocks	\$280.04
105932	Ready Access Padlock Station (Unfilled)	\$88.20



Ready Access Storage Stations

www.BradyID.com/lockouttagout

Ready Access Lockout Station

- Made of thermformed polypropylene for rugged durability
- Semi-transparent hinged cover with locking mechanism protects contents from harsh environments and prevents unauthorized access
- Slots in back for wall mounting
- Attachable carrying handle facilitates easy portability
- 4 detachable hanging hooks
- Storage compartment (4.25"H x 16"W x 5.12"D)
- Dimensions: 17" H x 17"W x 6.75"D

Station Only

Catalog No.	Description	Price Each
105942	Ready Access Lockout Station (unfilled)	\$106.83



Pictured Ready Access Valve & Electrical Lockout Station (105935)

Ready Access Valve Lockout Station

Components:

- 1 Ready Access Lockout Station (105942)
- 2 Adjustable Gate Valve Lockouts (64057)
- 1 All Purpose Cable Lockout (50943)
- 2 Ball Valve Lockouts (BS07A)
- 2 1" Group Lockout Hasps (65375)

- 1 1.5" Group Lockout Hasp (65376)
- 6 Keyed different safety padlocks (99552) or steel padlocks (99500)
- 6 Heavy duty, re-usable lockout tags (65520) w/ nylon cable ties

Catalog No.	Description	Price Each
105936	Valve Lockout Station (No Padlocks)	\$310.38
105937	Station w/ 6 Safety Padlocks	\$393.60
105938	Station w/ 6 Steel Padlocks	\$384.60

Ready Access Electrical Lockout Station

Components:

- 1 Ready Access Lockout Station (105942)
- 2 3-in-1 Electrical Plug Lockouts (PL023)
- 1 Mini Cable Lockout (50940)
- 2 120/277V Clamp-On Breaker Lockouts w/cleats (65396)
- 2 480/600V Clamp-On Breaker Lockouts w/cleats (65397)
- 2 Universal Multipole Breaker Lockouts (66321)
- 1 Oversized Breaker Lockout (65329)
- 2 1" Group Lockout Hasps (65375)

- 1 1.5" Group Lockout Hasps (65376)
- 6 Keyed different safety padlocks (99552) or steel padlocks (99500)
- 6 Heavy duty, re-usable lockout tags (65520) w/ nylon cable ties

Catalog No.	Description	Price Each
105939	Electrical Lockout Station (No Padlocks)	\$290.14
105940	Station w/ 6 Safety Padlocks	\$374.47
105941	Station w/ 6 Steel Padlocks	\$365.48

Ready Access Valve & Electrical Lockout Station

Components:

- 1 Ready Access Lockout Station (105942)
- 1 Adjustable Gate Valve Lockout (64057)
- 1 All Purpose Cable Lockout (50943)
- 1 Ball Valve Lockout (BS07A)
- 1 3-in-1 Electrical Plug Lockout (PL023)
- 2 120/277V Clamp-On Breaker Lockouts w/cleats (65396)
- 1 480/600V Clamp-On Breaker Lockout w/cleat (65397)
- 2 Universal Multipole Breaker Lockouts (66321)

- 2 1" Group Lockout Hasps (65375)
- 1 1.5" Group Lockout Hasp (65376)
- 6 Keyed-different safety padlocks (99552) or steel padlocks (99500)
- 6 Heavy duty, re-usable lockout tags (65520) w/ nylon cable ties

Catalog No.	Description	Price Each
105933	Valve & Electrical Station (No Padlocks)	\$314.87
105934	Station w/ 6 Safety Padlocks	\$399.22
105935	Station w/ 6 Steel Padlocks	\$390.22



May We Also Suggest

Combination Padlock for the Ready Access Station Door. See details on page 201.



Lockout Stations

www.BradyID.com/lockouttagout



**Extra-Large Lockout Station
(Open Style Without Doors)**



**Extra-Large Lockout Station
(With Lockable Acrylic Doors)**

Extra-Large Lockout Station

- Provides everything you need to lock out both mechanical and electrical control points
- Includes Universal Valve Lockout (page 212) and All Purpose Cable Lockout (see page 210)
- Constructed of sturdy polystyrene with pre-drilled holes for easy wall mounting
- Pegboard-style holes for hooks drilled into back and sides (8 hooks supplied standard)
- Built-in lock rail holds 20-25 locks depending on lock size
- Dimensions: 30"h x 25"w x 5 1/4"d
- Available with or without lockable acrylic doors
- Components:
 - 1 All Purpose Cable Lockout w/ 8' Sheathed Cable (50943)
 - 1 Large Univ. Valve Lockout w/ Blocking Arm (50899 and 65403)
 - 2 120V Snap-On Breaker Lockouts (65387)
 - 2 120/277V Clamp-On Breaker Lockouts (65396)
 - 2 480/600V Clamp-On Breaker Lockouts (65397)
 - 2 Universal Multi-Pole Breaker Lockouts (66321)
 - 1 Oversized Breaker Lockout (65329)
 - 2 Cleats for 120/277V Clamp-On Lockouts (65404)
 - 2 Cleats for 480/600V Clamp-On Lockouts (65406)
 - 1 Wall Switch Lockout (65392)
 - 1 110V Electrical Plug Lockout (65674)
 - 1 3-in-1 Electrical Plug Lockout (PL023)
 - 1 1/4" - 1" Ball Valve Lockout (65666)
 - 1 1 1/4" - 3" Ball Valve Lockout (65669)
 - 2 1" - 2 1/2" Gate Valve Lockouts (65560)
 - 1 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
 - 2 Labeled Lockout Hasps (65960)

Padlock Options:

- Choose between 18 keyed-different safety padlocks (99552) or 18 steel padlocks (99500).
- Padlocks come with 25 heavy duty, re-usable lockout tags (65520) and nylon cable ties

Open Style Without Doors

Catalog No.	Description	Price Each
99693	Station w/ Components and 18 Brady Safety Padlocks, 25 Tags	\$1,091.78
99694	Station w/ Components and 18 Brady Steel Padlocks, 25 Tags	\$1,081.23
50993	Extra-Large Lockout Station (unfilled)	\$431.76

Enclosed Style With Lockable Acrylic Doors

Catalog No.	Description	Price Each
99696	Station w/ Components and 18 Brady Safety Padlocks, 25 Tags	\$1,133.67
99700	Station w/ Components and 18 Brady Steel Padlocks, 25 Tags	\$1,123.21
50995	Extra-Large Enclosed Lockout Station (unfilled)	\$498.32

Large Lockout Station

- Provides everything you need for locking out all types of valves and plugs
- Includes Universal Valve Lockout (page 212) and All Purpose Cable Lockout (see page 210)
- Constructed of sturdy white polystyrene with predrilled holes for easy wall mounting
- Pegboard-style holes for hooks drilled into back (6 hooks supplied standard)
- Built-in lock rail holds 15 - 20 locks depending on lock size
- Dimensions: 26"h x 19 1/2"w x 5"d
- Available with or without lockable acrylic doors
- Components:
 - 1 All Purpose Cable Lockout w/ 8' Sheathed Cable (50943)
 - 1 Large Univ. Valve Lockout w/ Blocking Arm (50899 and 65403)
 - 1 110V Electrical Plug Lockout (65674)
 - 1 3-in-1 Electrical Plug Lockout (PLO23)
 - 1 1/4" - 1" Ball Valve Lockout (65666)
 - 1 1" - 2 1/2" Gate Valve Lockout (65560)
 - 1 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)
 - 2 Labeled Lockout Hasps (65960)
- Padlock Options:
 - Choose between 12 keyed-different safety padlocks (99552) or 12 steel padlocks (99500).
 - Padlocks come with 25 heavy duty, re-usable lockout tags (65520) and nylon cable ties

Open Style Without Doors

Catalog No.	Description	Price Each
99699	Station w/ Components and 12 Brady Safety Padlocks, 25 Tags	\$678.14
99697	Station w/ Components and 12 Brady Steel Padlocks, 25 Tags	\$671.17
50994	Large Lockout Station (unfilled)	\$266.25

Enclosed Style With Lockable Acrylic Doors

Catalog No.	Description	Price Each
99703	Enclosed Station w/ Components and 12 Brady Safety Padlocks, 25 Tags	\$729.64
99704	Enclosed Station w/ Components and 12 Brady Steel Padlocks, 25 Tags	\$722.68
50996	Large Enclosed Lockout Station (unfilled)	\$321.05



Large Lockout Station
(Open Style Without Doors)



Large Enclosed Lockout Station
(With Lockable Acrylic Doors)

Lockout Station V-Sign

- Enhance the visibility of your Lockout Station with this V-shaped polyethylene sign
- Sign size: 8" x 9" x 1" flange (overall width is 14")

Catalog No.	Descriptions	Price Each
66328	Lockout Stations V-Sign	\$33.10



Lockout Stations

www.BradyID.com/lockouttagout



Small Lockout Station

- Provides everything you need for locking out all types of electrical control points
- Includes Mini Cable Lockout (see page 211)
- Station constructed of sturdy white polystyrene with predrilled holes for easy wall mounting
- Built-in lock rail holds 10-15 locks depending on lock size
- Pegboard-style holes for hooks drilled into back (4 hooks supplied standard)
- Dimensions: 18"H x 12"W x 4"D

Small Lockout Station with Brady Safety Padlocks

Catalog No.	Description	Price Each
99706	Station w/ Components & 6 Brady Safety Padlocks, 12 Tags	\$458.58
99707	Station w/ Components & 6 Brady Steel Padlocks, 12 Tags	\$455.20
50997	Small Lockout Station (unfilled)	\$189.94

Components:

- 1 - Mini Cable Lockout (50940)
- 2 - 120V Snap-On Breaker Lockouts (65387)
- 2 - 120/277V Clamp-On Breaker Lockouts w/cleats (65396)
- 2 - 480/600V Clamp-On Breaker Lockouts w/cleats (65397)
- 2 - Universal Multi-Pole Breaker Lockouts (66321)
- 1 - Oversized Breaker Lockout (65329)
- 1 - Wall Switch Lockout (65392)
- 1 - 110V Electrical Plug Lockout (65674)
- 1 - 3-in-1 Electrical Plug Lockout (PLO23)
- 1 - Small fuse blockout (65690)
- 1 - Large fuse blockout (65691)
- 2 - Labeled Lockout Hasps (65960)

Padlock Options:

- Choose between 6 keyed-different safety padlocks (99552) or 6 steel padlocks (99500).
- Padlocks come with 12 heavy duty, re-usable lockout tags (65520) and nylon cable ties



Combined Lockout / Group Lockout Box Station

- All metal, yellow powder-coated cabinet comes with one adjustable shelf (extra shelves available)
- Capable of being locked closed
- Lockout safety tips printed on inside door
- Lock box attaches to bottom of cabinet, accommodates 8-10 locks depending on lock size
- Cabinet dimensions: 16"H x 14"W x 6"D
- Lock box dimensions: 6"H x 15"W x 3"D

Components:

- 1 - 120V Snap-On Breaker Lockouts (65387)
- 1 - 120/277V Clamp-On Breaker Lockout w/cleats (65396)
- 1 - 480/600V Clamp-On Breaker Lockout w/cleats (65397)
- 1 - Universal Multi-Pole Breaker Lockout (66321)
- 1 - Oversized Breaker Lockout (65329)
- 1 - Wall Switch Lockout (65392)
- 1 - 110V Electrical Plug Lockout (65674)
- 1 - 3-in-1 Electrical Plug Lockout (PLO23)
- 1 - 1" - 2 1/2" Gate Valve Lockout (65560)
- 1 - 1" - 6 1/2" Adjustable Gate Valve Lockout (64057)

Padlock Options:

- Choose between 6 keyed-different safety padlocks (99552) or 6 steel padlocks (99500).
- Padlocks come with 12 heavy duty, re-usable lockout tags (65520) and nylon cable ties

Catalog No.	Description	Price Each
99709	Station w/ Components & 6 Brady Safety Padlocks, 12 Tags	\$392.39
99710	Station w/ Components & 6 Brady Steel Padlocks, 12 Tags	\$375.62
LC252M	Metal Lockout Cabinet (unfilled)	\$190.75
LG252M	Metal Wall Lock Box (Lock Box Only)	\$107.13
LC254M	Extra Shelf	\$11.86

Prinzing Kits & Stations

www.BradyID.com/lockouttagout

Kits shown on this page use mostly Prinzing devices, some of which are not sold separately in this catalog.



Economy Lockout Kit (LKX)

- Our economy kit provides 9 components to ensure equipment is either de-energized or locked out in accordance with OSHA regulation 1910.47

Lockout Kit - Complete Set (LKXSET)

- Includes all components of the Economy Lockout Kit (LKX), plus the Sign & Rack (LKX-Rack) which conveniently holds the kit's carrying case.



Catalog Number	Description	Price Each
LKXSET	Lockout Kit - Complete Set	\$146.96
LKX	Economy Lockout Kit w/Toolbox	\$119.76
LKX-Rack	Sign & Rack only	\$43.61
LKX-TKLBOX	Toolbox only	\$38.98

Economy Lockout Kit Components:

- 3 - 1 1/2" Steel Lockout Hasps (T220)2
- 3 - Blue Prinzing Padlocks (LC041-BU)
- 14 - 2 Padlock Identifier Stickers (LID-2)
- 1 - pkg. (10) - Lockout Tags with Ties (LT10)
- 3 - Single Pole Breaker Lockouts (BL01)
- 2 - Multi Pole Breaker Lockouts (BL03)
- 1 3-in-1 Electrical Plug Lockout (PL023)
- 1 - Lockout Training Booklet (2112X)
- 1 - Rugged Polyethylene Carrying Case (7"H x 12"W x 5"D)

Lockout Kit - Complete Set Includes all of the above, plus the Sign & Rack (LKX-Rack)



Ultimate Lockout Kit

- The ultimate portable solution for a very wide range of lockout applications

Components:

- 1 - Safetee™ Donut 1" - 2 1/2" (SD02)
- 1 - Safetee™ Donut 5" - 6 1/2" (SD06)
- 1 - Ball Valve Lockout (BS07A)
- 1 - Ball Valve Lockout (BS08A)
- 1 - Electrical Plug / Pneumatic Lockout (PL027E)
- 10 - "Danger Do Not Operate" Lockout Tags (LT10)
- 1 - Cable Lockout Device (CABLO)
- 2 - No-hole Breaker Lockout (BL04)
- 2 - Breaker Lockout, Triple-pole (BL03)
- 1 - Breaker Lockout, Multi-pole (BL07)
- 2 - 1 1/2" Steel Lockout Hasp (T220)
- 1 - Wall Switch Lockout (WSLO)
- 1 - Lockout Safety Training Booklet (2112X)
- 1 - 120-600 AC Voltage Sensor (ESAC600)
- 3 - Prinzing Padlocks 3/4" Blue (LC041-BU)
- 1 - Lockout Bag "Duffel Style" (LX980E)

Catalog #	Description	Price
LK981E	Ultimate Lockout Kit	\$393.08
LK980E	Lockout Bag Only	\$65.73



Industrial Strength Lockout Station

- Lockable all metal, yellow powder coated cabinet comes with one adjustable shelf (extra shelves available)
- Lockout safety tips are conveniently located inside of door for frequent reminders of proper lockout procedures
- Can be wall mounted or easily transported
- Station size: 16"H x 14"W x 6"D

Components:

- 3 - Red Safety padlocks (99552)
- 3 - Yellow Safety padlocks (99570)
- 1 - Safetee™ Donut - 2 1/2" - 5" (SD04)
- 1 - Safetee™ Donut - 1" - 2 1/2" (SD02)
- 1 - Single pole breaker lockout (BL01)
- 10 - Lockout tags with ties (LT10)
- 2 - Multi pole breaker lockout (BL03)
- 1 - 1" Multiple lockout device (T218)
- 1 - Single pole breaker lockout (BL04)
- 1 - 1 1/2" Multiple lockout device (T220)
- 1 - 3-in-1 Electrical plug lockout (PL023)
- 1 - Small plug lockout (PLO21)

Catalog #	Description	Price
LC251M	Industrial Strength Lockout Station	\$414.85
LC252M	Cabinet Only	\$190.73



Safety Lockout Center (3001)



English/Spanish version (3002)

Safety Lockout Center

- Provides ready access to locks, tags, lockout devices and information
- Made of tough acrylic plastic
- Station size: 30"H x 24"W x 4 1/2"D

(3001) Components:

- 6 - Multi-color steel padlocks
- 2 - pkg (10)lockout tags with ties (LT10)
- 5 - 1 1/2" multiple lockout devices (T220)
- 1 - pkg (25)Lockout Safety booklets (2112X)

(3002) Components:

- 6 - Multi-color padlocks
- 2 - pkg (10) Bilingual lockout tags with ties (TG400B-10)
- 5 - 1 1/2" multiple lockout devices (T220)
- 15 - English Lockout Safety booklets (2112X)
- 10 - Spanish Lockout Safety booklets (2112SPX)

Catalog #	Description	Price
3001	Safety Lockout Center	\$296.37
3012	Board Only (3001 model)	\$134.70
3002	Bilingual Safety Lockout Center	\$299.31
3013	Board Only (3002 model)	\$134.70

OSHA Tag Requirements

The following requirements apply only to tags used as tagout devices (i.e., tags used alone without locks). Tags used in combination with locks are not required to meet the same restrictions as tagout devices.

TAGOUT DEVICES MUST:

- Be provided by the employer
- Be standardized by size, shape or color
- Be distinguishable from tags used for other purposes
- Be understandable to all employees
- Identify the individual who applied the tag
- Withstand the usage environment to which they are exposed for the maximum period of time that exposure is intended. Tag should not deteriorate or the message become illegible when exposed to weather, wet or damp conditions, chemical or corrosive environments.
- Employ a means of attachment that is substantial enough to prevent accidental removal. The means of attachment must be of a non-reusable type, attachable by hand, self-locking, and non-releasable with a minimum unlocking strength of no less than 50 pounds.
- Warn against hazardous conditions if the machine or equipment is energized.
- Tag shall also include a legend such as the following:
Do Not Operate, Do Not Start, Do Not Open, Do Not Close, etc.



How to Order Tags

- Determine the best tag material below for your application
- Choose the tag legend for your tag
- Order by part number for desired reverse side legend
- Standard package: 25 tags

Description	Size	Price Each
Heavy Duty Polyester (B-837)	5½" x 3"	\$65.50
Economy Polyester (B-851)	5¾" x 3"	\$39.43
Cardstock (B-853)	5¾" x 3"	\$20.19

Tag Materials

Heavy Duty Polyester (B-837)

- Durable polyester laminate completely encapsulates and protects graphics.
- Withstands moisture, grease, chemicals, and extreme temperatures.
- Accepts pencil, pen and marker. Pen and marker can be completely erased using isopropyl alcohol, allowing for repeated use!
- Heavy duty construction withstands up to 80 lbs of pull force, preventing accidental removal.
- 3/8" diameter heavy-duty brass grommet accepts most padlock shackles.
- Tags come with OSHA-compliant nylon fasteners

Economy Polyester (B-851)

- Rigid polyester surface is easy to write on and stays legible longer than cardstock
- Exceeds OSHA 50 lb. pull requirement for tagout devices
- 3/8" diameter rolled brass eyelet accepts most padlock shackles
- Tags come with OSHA-compliant nylon fasteners

Cardstock (B-853)

- Cost-effective tags designed for one-time use
- Does NOT meet OSHA 50 lb. pull test for tagout devices, but can be used in conjunction with locks (see OSHA Tag Requirements above)
- 3/8" diameter rolled brass eyelet accepts most padlock shackles
- Tags come with attachment strings

Reverse Side Options

Reverse Side B

DANGER

This energy source has been **LOCKED OUT!**

Unauthorized removal of this lock/tag may result in immediate discharge.

Remarks: _____

Reverse Side F

DANGER

This energy source has been **LOCKED OUT!**

Only the individual who signed the reverse side may remove this lock/tag.

Remarks: _____

Reverse Side G

PELIGRO

¡NO HACER FUNCIONAR!

This lock/tag may only be removed by:

Name _____

Date _____

NOMBRE _____

FECHA _____

DANGER

DO NOT OPERATE

This lock/tag may only be removed by:

Name _____

Date _____

DANGER

DO NOT OPERATE

This lock/tag may only be removed by:

Name _____

Date _____

DANGER

DO NOT OPERATE

I certify that the following tasks have been performed to lockout this equipment.

- Identified all potential hazards and energy sources
- Informed operator supervisor about work to be done.
- Prepared equipment for shutdown
- Shutdown/turned off equipment
- Isolated and locked out energy sources
- Released all stored energy
- Tested equipment to zero energy state
- Cleared personnel tools before and after job
- Removed locks and tags

This lock/tag may only be removed by:

Name _____

Job _____

Date _____

DANGER

LOCKED OUT

DO NOT OPERATE

This lock/tag may only be removed by:

Name _____

Date _____

Heavy Duty Polyester (B-837)

Rev. Side B - 65502	Rev. Side B - 65520	Rev. Side B - 65515	Rev. Side B - 65526
Rev. Side F - 65535	Rev. Side F - 65525	Rev. Side F - 65524	Rev. Side F - 65527
Rev. Side G - 65670	Rev. Side G - 65671	-	-

Economy Polyester (B-851)

Rev. Side B - 66050	Rev. Side B - 66063	Rev. Side B - 66061	Rev. Side B - 66066
Rev. Side F - 66051	Rev. Side F - 66064	Rev. Side F - 66062	Rev. Side F - 66067
Rev. Side G - 66052	Rev. Side G - 66065	-	-

Cardstock (B-853)

Rev. Side B - 65407	Rev. Side B - 65451	-	Rev. Side B - 65454
Rev. Side F - 65408	Rev. Side F - 65452	Rev. Side F - 65450	Rev. Side F - 65455
Rev. Side G - 65440	Rev. Side G - 65453	-	-

DANGER

DO NOT OPERATE

Maintenance Department

This lock/tag may only be removed by:

Name _____

Date _____

DANGER

DO NOT OPERATE

Electricians At Work

This lock/tag may only be removed by:

Name _____

Date _____

DANGER

DO NOT OPERATE

Production

This lock/tag may only be removed by:

Name _____

Date _____

DANGER

DO NOT OPEN

This lock/tag may only be removed by:

Name _____

Date _____

DANGER

DO NOT START

This lock/tag may only be removed by:

Name _____

Date _____

Heavy Duty Polyester (B-837)


Rev. Side B - 65503	Rev. Side B - 65504	-	Rev. Side B - 65506	Rev. Side B - 65505
Rev. Side F - 65521	Rev. Side F - 65522	-	Rev. Side F - 65534	Rev. Side F - 65523

Economy Polyester (B-851)

Rev. Side B - 66053	Rev. Side B - 66055	Rev. Side B - 50198	-	-
Rev. Side F - 66054	Rev. Side F - 66056	Rev. Side F - 50199	Rev. Side F - 66060	-

Cardstock (B-853)

Rev. Side B - 65441	Rev. Side B - 65443	-	Rev. Side B - 65447	Rev. Side B - 65445
Rev. Side F - 65442	Rev. Side F - 65444	Rev. Side F - 50250	Rev. Side F - 65448	Rev. Side F - 65446



Peel away liner

Self-Laminating Photo Tags

- Include employee photos for easy identification and greater impact
- Constructed of durable B-851 polyester with 1 mil polyester overlay on front
- 10 tags and nylon fasteners per package

Catalog No.	Size	Price Each
65501	5 3/4" x 3"	\$23.11
96222	7" x 4"	\$24.16

DANGER

DO NOT OPERATE

Do not remove this lock. It is here to protect my life.

PLACE PHOTO HERE

Name _____

Dept. _____

Front

DANGER

DO NOT REMOVE THIS TAG

Remarks _____

SEE OTHER SIDE

Back

Two-Part Perforated Tags

Two-part tags provide enhanced operational control and record-keeping. Stub is removed when tag is attached to a lockout point. Only the employee in possession of the stub has the authority to remove the tag. After the job is done, stub is returned to management for verification and monitoring of lockout/tagout activity in the plant. Matching identification numbers are printed on each part.



Heavy Cardstock Tags

- Economical cardstock tags are easy to write on using pen, pencil or permanent marker
- Employs 3/8" rolled brass eyelet that resists tearing
- Tie strings included for quick, easy attachment
- Dimensions: 7.5" x 4"
- Standard package: 25 tags

Catalog No.	Description	Price Each
105372	Equipment Locked Out	\$19.94
105373	Do Not Operate	\$19.94

Plastic Tags

- 10 mil-thick polyester enhances durability and makes it easy to remove chemicals, grease and grime.
- Write-on surface accepts marker, pen or pencil.
- Weatherproof for indoor or outdoor use.
- Employs 3/8" rolled brass eyelet that fits over most padlock shackles.
- Nylon cable ties included for easy, secure attachment
- Dimensions (h x w): 7.5" x 4"
- Standard package: 25 tags

Catalog No.	Description	Price Each
105370	Equipment Locked out	\$61.06
105371	Do Not Operate	\$61.06



Tags w/ Detachable Key Stub

Perforated cardstock tag comes with detachable key stub, making it easy to match up tags attached to padlocks with the right key. Matching identification numbers are printed on each part.

- Heavy cardstock accepts pencil, pen or marker
- Tie strings provided for easy tag attachment
- 1"-diameter metal ring provided for attaching stub to key
- Dimensions (h x w): 5 3/4" x 3"
- Standard package: 25 tags

Catalog No.	Description	Price Each
105368	Equipment Locked Out	\$32.51
105369	Do Not Operate	\$32.51



Padlock Tags

- Calendered vinyl accepts pencil, pen or marker.
- Employs 3/8" metal grommet that fits over most padlock shackles.
- Dimensions (h x w): 3" x 2" (grommet adds another 1" to height)
- Sold individually

Catalog No.	Description	Price Each
105722	Equipment Locked Out	\$2.39
105723	Do Not Operate	\$2.39
105724	Do Not Operate - English/Spanish	\$2.39

Tag Holders And Fasteners

www.BradyID.com/lockouttagout



1-Pocket Economy Tag Holder

- Compact, clear plastic holder is designed to hold 50 tags, ties and a marking pen
- Comes with adhesive strips, magnetic strips, and screws for mounting in a variety of ways
- Holder dimensions: 7 1/2"H x 4 1/2"W x 1 1/2"D
- Tags and pen not included

Cat. No.	Description	Price Each
TH2	1-Pocket Economy Tag Holder	\$14.10



Pocket Premium Tag Center

- Acrylic center features 8 pockets for displaying and dispensing tags
- Each polystyrene pocket holds up to 30 tags
- Four pre-drilled holes for wall mounting
- Board dimensions: 15 3/4"H x 23 1/2"W x 2"D
- Tags not included

Cat.No.	Description	Price Each
TC8	8-Pocket Premium Tag Center	\$52.82



10-Pocket Tag Safety Station

- Made of rugged polycarbonate
- Four pre-drilled holes for wall mounting
- Board dimensions: 22"H x 16 1/2"W x 2 1/4"D
- Tags not included

Cat. No.	Description	Price Each
81773	10-Pocket Tag Safety Station	\$110.28



Tag Fasteners

- Three fastener styles available to meet every application
- Nylon fasteners meet OSHA requirements for attaching tagout devices
- Standard package: 100

Cat. No.	Description	Qty.	Price
81760	26 Gauge Wire, 12" long	100	\$14.20
81761	Reusable Beaded Ties 8" long	100	\$55.53
81762	Nylon Fasteners 8" long	100	\$12.21



Magnetic Backed Envelope Open-Ended



Zip Lock Envelope

Magnetic And Zip Lock Protective Envelopes

- Transparent, durable vinyl construction protects against weather damage and soiling
- Ideal for indoor or outdoor use
- Protects tags and data cards on machinery, valves, switches, controls, and more

Magnetic Backed With Open End

Catalog No.	Size	Qty.	Price
81769	4 1/2" x 6 1/2"	10/pkg.	\$43.82
81770	5 1/2" x 8 1/2"	10/pkg.	\$49.68

Zip Lock Envelope

Catalog No.	Size	Qty.	Price
81765	(w/o grommet) 4 1/2" x 6 1/2"	10/pkg.	\$32.07
81766	(w/grommet) 4 1/2" x 6 1/2"	10/pkg.	\$52.03
81767	(w/o grommet) 5 1/2" x 8 1/2"	10/pkg.	\$34.76
81768	(w/grommet) 5 1/2" x 8 1/2"	10/pkg.	\$54.12

Keep your tags organized and easily accessible!

Padlocks

www.BradyID.com/lockouttagout

OSHA Lockout Device Requirements

LOCKOUT DEVICES **MUST**:

- Be provided by the employer
- Be standardized by size, shape or color
- Be distinguishable from locks used for other purposes. Lockout locks should only be used for lockout!
- Identify the individual who applied the lock (both tags and lock labels are acceptable for this purpose)
- Be capable of withstanding the usage environment and must be strong enough to prevent removal except by using excessive force with special tools, such as bolt cutters.
- Most importantly, whenever lockout devices are applied, they must remain under the exclusive control of the individual who attached them. No employee should be able to open a lock attached by someone else.

KEYING & CHARTING OPTIONS

Keyed Different

- Brady padlocks come “keyed different” when purchased from stock. This means that the key for one lock should not open another. Brady padlocks use 5- or 6-pin cylinders. Moreover, both cylinders and keys are precision-machined to exacting standards. This enables us to offer a greater number of unique keys than other locks with the same number of pins, making it highly unlikely that you will ever receive a duplicate lock.
- To guarantee that each lock is different, we can chart your locks, ensuring that each Brady padlock you receive is different from the others (see below).




Keyed Alike

- When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee. Remember, however, that under OSHA regulations no employee should be able to open a lock applied by someone else. Therefore, keyed alike locks from the same set should never be distributed to multiple employees.



Master Keyed

- A master key can be used to open multiple locks that are keyed differently. This allows supervisors to easily remove a lock in the event of an emergency. In order for employees to retain exclusive control, master keys should be kept in a secure location that is accessible only to management.



Key Charting

- Brady can track or “chart” your key codes upon request in order to simplify ordering of replacement locks and to avoid duplicates when ordering additional locks.

There is no extra charge for charting. Call for details.

Choose the lock that’s best suited for the job!

	COMPACT SAFETY PADLOCKS	SAFETY PADLOCKS	ALUMINUM PADLOCKS	KEY-RETAINING STEEL PADLOCKS	STEEL PADLOCKS
Compact, lightweight	✓	✓	✓		
Nonconductive body & keyway	✓	✓			
Most corrosion resistant	✓	✓	✓	✓	✓
Most spark resistant	✓	✓			
Most tamperproof		✓	✓	✓	✓
Most rugged		✓		✓	✓

Safety Padlocks The Ultimate Lockout Lock!

Brady Safety Padlocks complies with all OSHA requirements and is a safer alternative to metal locks for lockout applications. The body is nonconductive, while the unique key cylinder prevents electricity from traveling from the shackle to the key, protecting workers when key is inserted.

Safety Padlocks also deliver superior corrosion resistance. Third-party tests confirm that Brady outperforms the leading competitor when subjected to repeated salt water sprays.

- Superior temperature, chemical and corrosion resistance
- "Danger" and "Property of" labels provided in English, Spanish, and French and are printed on 100% recycled paper
- Reserved paracentric keyway provides optimal security (prevents someone from getting a copy made at a local key shop)
- Key-retaining safety feature prevents key from being removed until shackle is securely closed
- Locks come keyed differently or in keyed-alike sets. Custom keying and charting also available (see page 198)
- Lock bodies can be custom laser engraved upon request
- One key is supplied with each padlock for safer key management



NEW!

Compact Safety Padlocks

- Extremely compact and lightweight - the smallest safety lock on the market
- Fits in small spaces easily (circuit breaker panels, etc) and is ideal lock for electrical contractors/maintenance/electricians
- 5-pin cylinder - can support same keying system as our current Safety Lock
- Fiberglass reinforced nylon body for extra impact resistance
- Aluminum shackle gives superior spark and corrosion resistance
- Service temperature: 0-250 degrees F (-20 - 120 degrees C)
- Lock body dimensions: 1 2/5" H, 1 1/5" W, 5/8" D
- Shackle clearance: 1"; shackle diameter 1/5"

Compact Safety Padlocks (Available November 2011)

Color	Keyed Different 1 Padlock/Pack Price \$10.90	Keyed Different 6 Padlocks/Pack Price \$63.80	Keyed Alike 3 Padlocks/Pack Price \$36.21	Keyed Alike 6 Padlocks/Pack Price \$72.42
Red	143150	118926	118953	118954
Green	143152	118927	118955	118956
Orange	143154	118928	118957	118958
Blue	143156	118929	118959	118960
Yellow	143158	118930	118961	118962
Brown	143160	118931	118963	118964
White	143162	118932	118965	118966
Purple	143164	118933	118967	118968
Black	143166	118934	118969	118970

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.



Safety Padlocks

- Lightweight, nonconductive and non-sparking body
- Special 6-pin cylinder resists tampering
- Fiberglass reinforced nylon body and triple-coated hardened steel shackle
- Service temperature: 0° - 250° F (-20° - 120° C)
- Lock body dimensions: 1 3/4" H x 1 1/2" W x 3/8" D
- Shackle clearance: 1 1/2"; shackle diameter: 1/4"

Safety Padlocks

Color	Keyed Different 1 Padlock/Pack Price \$13.50	Keyed Different 6 Padlocks/Pack Price \$79.41	Keyed Alike 3 Padlocks/Pack Price \$43.83	Keyed Alike 6 Padlocks/Pack Price \$87.65
Red	99552	51339	105886	105890
Blue	99556	51344	105887	105891
Green	99564	51345	105889	105893
Yellow	99570	51346	105888	105892
Orange	99576	51347	-	-
Black	99580	51353	-	-
Brown	103033	101956	118947	118948
Purple	104919	104916	118951	118952
White	143123	118925	118949	118950

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.

Steel Padlocks

www.BradyID.com/lockouttagout



Key Retaining Steel Padlocks

- Reinforced laminated steel withstands severe physical abuse
- Hardened steel shackle resists tampering, cutting, prying, and rusting
- Body plates individually coated for superior rust protection, offering 13 times better corrosion resistance than normal steel locks
- 5-pin cylinder offers more unique key cuts and increased tamper resistance
- Two shackle sizes: 3/4" or 2", shackle diameter: 17/64"
- Lock Body: 1 1/5" H, 1 5/16" W, 1" D
- Colored bumpers supplied for identification and protection (custom stamping available)
- Custom keying and charting also available (see page 198)
- One key supplied with each padlock for safer key management
- Lock labels sold separately and made from 100% recycled paper
- Made from recycled material
- Key retaining safety feature prevents key from being removed until closed
- Lighter weight than standard Laminated Steel Padlocks

(Available November 2011)

Key Retaining Steel Padlocks - 3/4" Shackle

Color	Keyed Different 1 Padlock/Pack Price \$11.14	Keyed Different 6 Padlocks/Pack Price \$65.24
Red	143126	118935
Green	143128	118936
Blue	143130	118937
Yellow	143132	118938
White	143134	118939
Black	143136	118940

(Available November 2011)

Key Retaining Steel Padlocks - 2" Shackle

Color	Keyed Different 1 Padlock/Pack Price \$13.92	Keyed Different 6 Padlocks/Pack Price \$81.92	Keyed Alike 3 Padlocks/Pack Price \$46.47	Keyed Alike 6 Padlocks/Pack Price \$92.94
Red	143144	118944	118977	118978
Green	143142	118943	118975	118976
Blue	143140	118942	118973	118974
Yellow	143148	118946	118981	118982
White	143146	118945	118979	118980
Black	143138	118941	118971	118972

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.



Steel Padlocks

- Reinforced laminated steel withstands severe physical abuse
- Hardened steel shackle resists tampering
- Body plates individually coated for superior rust protection
- 5-pin cylinder offers more unique key cuts, better tamper resistance than conventional 4-pin locks
- One key supplied with each padlock for safer key management
- Two shackle sizes: 3/4" or 2", shackle diameter: 17/64"
- Lock body: 1 1/5"H x 1 9/16"W x 7/8"D
- Colored bumpers supplied for identification and protection (custom stamping available)
- Locks come keyed-different. Custom keying and charting also available (see page 198)
- Lock labels sold separately

Steel Padlocks - 3/4" Shackle

Color	Keyed Different 1 Padlock/Pack Price \$12.08	Keyed Different 6 Padlocks/Pack Price \$70.99
Red	99500	51279
Blue	99504	51280
Green	99508	51281
Yellow	99512	51282
Orange	99516	51283
Black	99520	51284
Brown	101957	102696
Purple	104920	104917

Steel Padlocks - 2" Shackle

Color	Keyed Different 1 Padlock/Pack Price \$15.38	Keyed Different 6 Padlocks/Pack Price \$90.44	Keyed Alike 3 Padlocks/Pack Price \$49.44	Keyed Alike 6 Padlocks/Pack Price \$98.90
Red	99524	51290	105894	105898
Blue	99528	51291	105895	105899
Green	99533	51292	105897	105901
Yellow	99539	51297	105896	105900
Orange	99543	51298	-	-
Black	99548	51299	-	-
Brown	101958	102698	-	-
Purple	104921	104918	-	-

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.

Aluminum Padlocks

- Lightweight yet rugged with solid aluminum body and shackle - lightest-weight aluminum lock in the market and made from recycled material
- 6-pin cylinder offers more unique key changes, better tamper resistance
- Reserved paracentric keyway provides optimal security (prevents someone from getting a copy made at a local key shop)
- FDA approved lubricant in cylinder
- Anodized aluminum finish gives better fade resistance when used outdoors
- Key retaining safety feature prevents key from being removed until closed
- Aluminum shackle gives better corrosion resistance (four times better than the hardened chrome-plated steel shackle) and is spark resistant
- Two shackle sizes: 1" and 1 1/2", shackle diameter: 1/4"
- Lock body: 1 3/8"H x 1 1/2"W x 3/4"D
- Two keys supplied with each lock. Custom keying and charting also available (see pg 198)
- Lock labels sold separately (made from 100% recycled paper)



Aluminum Padlocks - 1" Shackle

Color	1 Padlock/Package Price \$15.38	6 Padlocks/Package Price \$90.44
Red	99608	51360
Blue	99609	51361
Green	99610	51362
Yellow	99611	51363
Orange	99612	51368
Black	99613	51369
Brown	104574	104575
Purple	104572	104573

Aluminum Padlocks - 1 1/2" Shackle

Color	Keyed Different 1 Padlock/Pack Price \$16.49	Keyed Different 6 Padlocks/Pack Price \$96.93	Keyed Alike 3 Padlocks/Pack Price \$52.75	Keyed Alike 6 Padlocks/Pack Price \$105.51
Red	99615	51370	105902	105882
Blue	99616	51371	105903	105883
Green	99617	51376	105881	105885
Yellow	99618	51377	105904	105884
Orange	99619	51378	-	-
Black	99620	50274	-	-
Brown	104578	104579	-	-
Purple	104576	104577	-	-

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.



Combination Padlock

- Compact, Lightweight
- 4-digit resettable code
- Steel shackle

Catalog #	Description	Price
101963	Combination Padlock	\$21.91



Safety Padlock Labels

Safety padlock labels help send a clear message to workers when a machine is down for service or maintenance. Labels are designed to fit Brady Safety Padlocks and are available in English.

Catalog #	Description	Price
51379	English (6/Pkg)	\$6.96



Steel Padlock Labels

- Made of durable B-826 vinyl and includes overlaminated strips for enhanced durability
- Writable using pencil, pen or marker
- Dimensions: 3/4"H x 4 1/2"W

Catalog #	Description	Price
50280	English (6/Pkg)	\$6.96
50281	Spanish (6/Pkg)	\$6.96
50283	French (6/Pkg)	\$6.96



Aluminum Padlock Labels

- Made of durable B-826 vinyl
- Writable using pencil, pen or marker
- Dimensions: 0.8"H x 1.1"W
- Contains 6 front and back labels

Catalog #	Description	Price
50289	English (6/Pkg)	\$6.96
50292	Spanish (6/Pkg)	\$6.96
50293	French (6/Pkg)	\$6.96

Lockout Boards

www.BradyID.com/lockouttagout

Lockout Boards

- Board made of 3/16"-thick yellow acrylic with acrylic lock rails
- Tag pockets made of clear polycarbonate, hold tags up to 3" wide



5-Lock Board

- Dimensions: 11 1/2"H x 15 1/2"W
- Includes 5 padlocks (99552 or 99500), one 1" metal hasp (65375), one 1 1/2" metal hasp (65376) and 12 heavy duty tags (65520)

Catalog #	Description	Price Each
51181	5-Lock Board (Filled w/ Brady Safety Padlocks)	\$210.41
51186	5-Lock Board (Filled w/ Brady 3/4" Steel Padlocks)	\$190.26
50989	5-Lock Board (Board Only)	\$96.72



10-Lock Board

- Dimensions: 13 1/2"H x 13 1/2"W
- Includes 10 padlocks (99552 or 99500), two 1" hasps (65375), two 1 1/2" hasps (65376) and 12 heavy duty tags (65520)

Catalog #	Description	Price Each
51187	10-Lock Board (Filled w/ Brady Safety Padlocks)	\$302.26
51188	10-Lock Board (Filled w/ Brady 3/4" Steel Padlocks)	\$296.53
50990	10-Lock Board (Board Only)	\$120.90



20-Lock Board

- Dimensions: 23 1/2"H x 11 1/2"W
- Includes 20 padlocks (99552 or 99500), two 1" hasps (65375), two 1 1/2" hasps (65376) and 24 heavy duty tags (65520)

Catalog #	Description	Price Each
51189	20-Lock Board (Filled w/ Brady Safety Padlocks)	\$518.81
51194	20-Lock Board (Filled w/ Brady 3/4" Steel Padlocks)	\$507.32
50991	20-Lock Board (Board Only)	\$181.32



36-Lock Board


- Dimensions: 21 1/2"H x 23 1/2"W
- Includes 36 padlocks (99552 or 99500), three 1" hasps (65375), three 1 1/2" hasps (65376) and 36 heavy duty tags (65520)

Catalog #	Description	Price Each
51195	36-Lock Board (Filled w/ Brady Safety Padlocks)	\$828.43
51196	36-Lock Board (Filled w/ Brady 3/4" Steel Padlocks)	\$807.74
50992	36-Lock Board (Board Only)	\$241.86

Padlock Stations

- Constructed of 14 gauge steel with red plastic coating
- Small station holds up to 4 padlocks (2 1/4"H x 3"W x 1 1/4"D)
- Large station holds up to 24 padlocks (3"H x 16"W x 1 1/4"D)
- Padlocks not included

Catalog #	Description	Price Each
LR060E	Small Padlock Station	\$20.77
LR360E	Large Padlock Station	\$32.48



Enclosed Padlock Storage Modules

- Provides safe storage and controls access to padlocks
- Constructed of sintra with lockable, transparent acrylic doors
- Each metal hook can hold 2 locks
- Two sizes available for holding 16 or 40 locks
- Padlocks sold separately

Catalog #	Description	Dimensions (H x W x D)	Price Each
65240	Small Padlock Storage Module	15" x 15" x 3 1/2"	\$258.06
65241	Large Padlock Storage Module	30" x 15" x 3 1/2"	\$347.07



Steel Padlock Control Centers

- Red powder-coated 22 gauge steel with white silk-screened graphics
- Each nickel coated metal hook can hold 2 locks
- Two sizes available for holding 16 or 32 locks
- Two keys supplied for cabinet lock
- Padlocks sold separately

Catalog #	Description	Dimensions (H x W x D)	Price Each
LR008E	Small Padlock Control Center	10" x 12" x 2"	\$104.64
LR018E	Large Padlock Control Center	15 1/2" x 18" x 2"	\$119.74



Padlock Centers

www.BradyID.com/lockouttagout

Padlock Management System

- Reduces theft by controlling access to locks!
- 7 different sizes hold from 1 to 75 locks (10 lock station shown)
- Each lock individually secured into a numbered port on the lock board
- Locks can only be removed by personnel with assigned access keys. Access key is retained in lock board until lock is returned.
- Employees photos can be applied to locks. See below for file requirements*

CST1154

Lock Boards with Locks/Size	Locks Per Unit
H 5 ⁵ / ₈ " x W 21 ³ / ₈ " x D 4"	5
H 7" x W 21 ³ / ₈ " x D 4"	10
H 10" x W 21 ³ / ₈ " x D 4"	15
H 17 ¹ / ₂ " x W 21 ³ / ₈ " x D 4"	25
H 32 ¹ / ₂ " x W 21 ³ / ₈ " x D 4"	50
H 47 ³ / ₈ " x W 21 ³ / ₈ " x D 4"	75

For Keyed Alike or Master Keyed Padlocks call your local Brady Distributor for pricing.



This tracking system can also be used to secure a wide variety of plant assets, including employee issued tools, electronics and maintenance equipment.

SPECIFY THE FOLLOWING TO ORDER YOUR MANAGEMENT SYSTEM

- 1 LOCKS PER UNIT** (Choose one)
- 5 locks (board size – 5³/₈" h x 21³/₈" w x 4" d)
 - 10 locks (board size – 7" h x 21³/₈" w x 4" d)
 - 15 locks (board size – 10" h x 21³/₈" w x 4" d)
 - 25 locks (board size – 17¹/₂" h x 21³/₈" w x 4" d)
 - 50 locks (board size – 32¹/₂" h x 21³/₈" w x 4" d)
 - 75 locks (board size – 47³/₈" h x 21³/₈" w x 4" d)

- 2 COLOR OF LOCKS** (Total must equal choice above)
- Yellow _____ Qty
 - Green _____ Qty
 - Red _____ Qty

- 3 KEYING**
- Keyed ALIKE Keyed DIFFERENT
 - Master Key w/ Keyed Alike Master Key w/ Keyed Different
 - _____ Qty of Master Keys _____ Qty of Master Keys

- 4 COLOR OF ACCESS KEYS** (Total must equal no. of locks)
- Yellow _____ Qty Green _____ Qty
 - White _____ Qty Blue _____ Qty
 - Red _____ Qty Silver _____ Qty
- (Other colors also available)

SPECIFY THE FOLLOWING TO ORDER ADDITIONAL LOCKS OR ACCESS KEYS

- 1 ADDITIONAL LOCKS**
- Yellow _____ Qty Green _____ Qty
 - White _____ Qty Blue _____ Qty
 - Red _____ Qty Silver _____ Qty

- 2 KEYING**
- Keyed Different
 - Keyed Alike
 - Master Key with Keyed Alike
 - _____ Qty of Master Keys
 - Master Key with Keyed Different
 - _____ Qty of Master Keys

- 3 ADDITIONAL ACCESS KEYS**
- Yellow _____ Qty Green _____ Qty
 - White _____ Qty Blue _____ Qty
 - Red _____ Qty Silver _____ Qty
- (Other colors also available)

LOCKOUT BOXES - A GREAT IDEA FOR GROUP LOCKOUT

For group lockout situations involving a large number of workers and equipment, lock boxes can offer a number of advantages over hasps.

HOW GROUP LOCKOUT BOXES WORK:

- Supervisor uses a single job lock on each energy control point to lock out equipment
- Keys for job locks are put in a lockout box
- Each worker applies his own lock to the lock box. As long as any one worker's lock remains on the lockout box, the keys to the job locks cannot be accessed, and the energy isolating devices cannot be operated. Each employee retains exclusive control, as required by OSHA.

HOW GROUP LOCKOUT BOXES CAN SAVE YOU LOTS OF MONEY:

- Example: Assume 5 workers need to lock out 10 energy control points
- Using hasps, 50 locks are required (all 5 workers must apply individual locks to each control point)
- Using a lockout box, only 15 locks are required (10 job locks applied to control points and 5 employee locks applied to lockout box). That's 70% fewer locks!
- Less weight hanging from the energy point – 1 lock instead of 5!
- Finally, checking the locks on the lock box allows you track who is still working. With hasps, you need to walk around to each energy control point to see whose lock is still in place.



Portable Metal Group Lockout Boxes

- Made of heavy duty steel, powder-coated for extra rust resistance
- 13 lock holes on lid, plus lockable clasp on front (locks not included)
- Standard lock box
Dimensions: 6"H x 9"W x 3½"D
When used for storage, holds up to 40 padlocks
- Extra –large lock box
Dimensions: 6"H x 7⅞"W x 9½"D
When used for storage, holds up to 75 padlocks

Catalog #	Description	Size	Price Each
65699	Red - Standard	9"W x 3½" D x 6"H	\$84.61 \$88.84
51171	Red - XL	7⅞"W x 9½" D x 6"H	\$98.65



Combined Lock Storage / Group Lockout Box

- Handy box features a lockable storage compartment and a group lockout compartment.
- Made of heavy duty steel, powder coated for extra rust resistance
- Group lockout compartment has clear Lexan window with keyhole slot
- Standard box
Overall dimensions: 12½"L x 7½"W x 6"D
Storage compartment size: 8½"L x 6"W x 6"D
Storage compartment holds approx. 50 padlocks
17 padlock holes in group lock box lid
- Large box
Overall dimensions: 15"L x 10½"W x 9"D
Storage compartment size: 10½"L x 9"W x 9"D
Storage compartment holds approx. 125 padlocks
34 padlock holes in group lock box lid

Catalog #	Description	Size	Price Each
105716	Standard	7½"W x 6"D x 12½"L	\$171.74
105717	Large	10½"W x 9" D x 15"L	\$249.04

Group Lockout Boxes

www.BradyID.com/lockouttagout



Portable Plastic Group Lockout Box

- Injection molded using Isoplast polymers for rugged durability
- Won't corrode! Excellent chemical and heat resistance properties
- Lock rails hold up to 16 padlocks (locks not included)
- Slot in front allows keys to be inserted when box is locked
- Transparent polycarbonate windows let you view contents
- Pre-drilled holes in back allow for easy wall-mounting
- Comes with 12 hooks for hanging keys, locks, etc., inside box
- Box body dimensions: 7 1/2"H x 8 1/2"W x 4 1/4"D
- Patent Applied For

Catalog #	Description	Price Each
50937	Portable Plastic Lock Box	\$71.05
50939	Extra Key Hooks (12/pkg)	\$7.56



Wall-Mounted Group Lockout Box

- Injection molded for extra durability
- Won't corrode! Excellent chemical and heat resistance properties
- Lock rails hold up to 8 padlocks
- Transparent window lets you view contents from outside
- Slot in front allows keys to be inserted when locked
- Pre-drilled holes in back allow for easy wall-mounting
- Comes with 6 hooks for hanging keys, locks, etc., inside
- Box body dimensions: 6 1/8"H x 4"W x 5 1/2"D

Catalog #	Description	Price Each
50938	Miniature Wall Lock Box	\$50.74
50939	Extra Key Hooks (12/Pkg)	\$7.56



Acrylic Wall-Mounted Group Lockout Boxes

- Made of acrylic plastic
- Pre-drilled holes in back for easy wall mounting
- Transparent front cover allows easy viewing of contents
- Pre-attached plastic hooks for hanging keys, tag stubs, etc.
- Available in 3 sizes

Catalog #	Dimensions (H x W x D)	Max. Number of padlocks	Number of key hooks	Price Each
LG003E	Small 6" x 6" x 2 1/2"	6	3	\$71.03
LG008E	Medium 7 1/2" x 12" x 2 1/2"	10	8	\$76.56
GLOBOX	Large 7 1/2" x 15 1/4" x 2 1/2"	14	18	\$96.43

Metal Wall-Mounted Group Lockout Boxes

- Made of durable, powder-coated steel with key slot on top.
- Includes clear Lexan window that slides out when locks are removed.
- Comes with key pegs and ID labels to simplify key management.
- Predrilled holes and hardware included for quick mounting.
- Small lock box:
 - Dimensions: 7"H x 8"W x 2 1/4"D
 - 7 key pegs that hold 5 keys each
 - 7 lock holes along bottom
- Large lock box:
 - Dimensions: 7"H x 16"W x 2 1/4"D
 - 15 key pegs that hold 5 keys each
 - 12 lock holes along bottom



Catalog #	Description	Price Each
105714	Small Metal Lock Box	\$122.65
105715	Large Metal Lock Box	\$147.20

Portable / Wall Group Lockout Box

- Made of yellow powder-coated metal
- Accommodates 8-10 locks (depending on lock size)
- Can be used alone or in combination with Metal Lockout Cabinet (see page 187)
- Dimensions: 6"H x 15"W x 3"D



Catalog #	Description	Price Each
LG252M	Prinzing Metal Wall Lock Box	\$107.13

SHOCK-STOP™ Group Lockout Box

- Combines lock box with storage board for hasps
- Lock box accepts up to 6 locks and provides rail for storing locks when not in use
- Comes standard with two SHOCK-STOP™ hasps
- Overall dimensions: 16 1/2"H x 10 1/2"W x 2 1/2"D
- Mounting hardware and instructions included

Catalog #	Description	Price Each
87692	Group Lock Box	\$194.26
87693	Hasp (5/pkg.)	\$80.21



Group Lockout Hasps

www.BradyID.com/lockouttagout



Steel Group Lockout Hasps

- Constructed of vinyl-coated high tensile steel w/ rest resistant plating
- Lock holes: 3/8" diameter
- Available in 1" and 1 1/2" diameter jaws
- Standard package: 12 hasps

Catalog #	Description	Price Each
65375	1" Diameter Jaws	\$97.18
65376	1 1/2" Diameter Jaws	\$115.93



Steel Group Lockout Hasps with Tabs

- Tamperproof interlocking tabs prevent unauthorized opening
- Constructed of case-hardened steel with rust proof plating and bright red vinyl insulation. Maximum 3/8" shackle diameter
- Available in 1" and 1 1/2" diameter jaws
- Standard package: 1 hasp

Catalog #	Description	Price Each
105718	1" Diameter Jaws	\$8.54
105719	1 1/2" Diameter Jaws	\$9.75



Corrosion-Resistant Group Lockout Hasps

- Manufactured from 12 gauge steel that is epoxy coated to give superior resistance to rust and added dielectric strength
- Yellow plastic coating is added to the lock area for visibility
- Standard package: 1 hasp
- Available in 1" and 1 1/2" diameter jaws
- Lock holes: 5/16" diameter

Catalog #	Description	Price Each
T220	Lockout Hasp - 1 1/2" diameter	\$7.97
T218	Lockout Hasp - 1" diameter	\$7.53



Aluminum Economy Group Lockout Hasps

- Non-sparking, aluminum small hasps are a great addition to your tool box
- Lightweight - only 1 1/2 ounces
- Maximum 3/8" shackle diameter
- Available in 1" and 1 1/2" diameter jaws
- Standard package: 1 hasp

Catalog #	Description	Price Each
105720	1" Diameter Jaws	\$8.13
105721	1 1/2" Diameter Jaws	\$9.29



Nonconductive Group Lockout Hasps

- Made of strong, rigid yellow plastic resin
- Has excellent electrical insulating characteristics
- Performs at low temperatures, excellent heat resistance
- Patent #7,124,606

Catalog #	Description	Price Each
LH220A-YW	Yellow Lockout Hasp	\$9.77
LH220A	Red Lockout Hasp	\$10.98

Group Lockout Hasps

www.BradyID.com/lockouttagout



SHOCK-STOP® Group Lockout Hasps

- Highly visible hasp uses stop sign design to draw attention
- Includes 6 lock holes and a slot for daisy-chaining hasps together
- Also sold with companion storage board and lock box
- Lock holes: 5/16" diameter
- Dimensions: 5 1/2"H x 3 3/8"W x 3/16"D

Catalog #	Description	Price Each
87693	Shock-Stop™ Hasps (5/pkg)	\$80.21



Non-Conductive Nylon Group Lockout Hasp

- Nonconductive nylon hasps accommodates up to 6 locks
- Withstands up to 1,000 lbs, yet weighs only 1 oz.
- Lock holes: 3/8" diameter
- Dimensions: 7"H x 1 3/4"W


Catalog #	Description	Price Each
99668	Nylon Lockout Hasp	\$9.07



Brady's Labeled Group Lockout Hasp is a combination Lockout Tag and Safety Lockout.

Labeled Group Lockout Hasps

- Constructed from tough 5052 anodized aluminum alloy
- Includes tamperproof locking tabs
- Write-on label surface accepts pencil, pen or marker
- Pen and pencil markings can be easily erased, allowing repeated use
- For permanent marking, use the marker sold below
- Lock holes: 5/16" diameter
- Dimensions: 7 1/4"H x 3"W x 3/16"D
- Standard pkg. 5



Reverse Side #1



Reverse Side #2

Labeled Lockout Hasps – Aluminum

Color	Reverse Side #1 Price \$78.77	Reverse Side #2 Price \$78.77
Red	65960	65970
Silver	65961	65971
Blue	65962	65972
Green	65963	65973
Gold	65964	65974
Combination	65967	65975

Also available in Spanish – call your local distributor for details.

Cable & Chain Lockouts

www.BradyID.com/lockouttagout

CABLE LOCKOUTS – GREAT VERSATILITY!

- The advantage of using cable lockouts is that they can be used in a wide variety of applications
- Cable lockouts can be used to lockout multiple disconnects, valves, etc. with one lockout device
- They can also be used to secure unusual energy isolating devices that are difficult to lock out using conventional means.
- More portable and easier to use than chains, cable lockouts devices are a great addition to any lockout program.




Lockout large gate valves, other oversized devices



Lockout multiple control points with a single device.

All Purpose Cable Lockout



Shown with non-conductive nylon cable

Sheathed metal cable

- Compact, lightweight body made of rugged Isoplast
- Ergonomic design makes it a “cinch” to tighten cable – hold device in one hand and cinch tight with the other!
- Superior chemical, corrosion and temperature resistance properties
- Two types of interchangeable cables:
 - Nonconductive nylon cable (1/8" diameter)
 - Sheathed metal cable (3/16" diameter, vinyl coating)
- Built-in cable loop keeps cable neatly coiled when stored, also keeps extra cable from dangling loose and posing a hazard when in use.
- 4 lock holes in handle accommodate most lock shackles and hasps
- Max. Service temperature of cables:
 - Sheathed Metal: -30° to 180° F
 - Non-Conductive Nylon: -40° to 200° F



Catalog #	Description	Price Each
50943	APCLO with 8' sheathed metal cable	\$47.93
50941	APCLO with 8' non-conductive nylon cable	\$50.62
50944	APCLO without cable	\$39.94

Sheathed Metal Cables Sold Separately

Catalog #	Description	Price Each
50947	Sheathed metal cable - 8'	\$10.10
50950	Sheathed metal cable - 12'	\$16.44
50953	Sheathed metal cable - 16'	\$21.53
50956	Sheathed metal cable - 20'	\$25.34

Nonconductive Nylon Cables Sold Separately

Catalog #	Description	Price Each
50945	Non-conductive Nylon cable - 8'	\$12.64
50948	Non-conductive Nylon cable - 12'	\$18.98
50951	Non-conductive Nylon cable - 16'	\$25.34
50954	Non-conductive Nylon cable - 20'	\$31.69

Cable & Chain Lockouts


www.BradyID.com/lockouttagout



Mini Cable Lockout

- Perfect for use on disconnect switches, small gate valves, etc.
- Extremely compact and portable. Cable stored internally.
- Push-button self-winding mechanism automatically cinches cable tight
- Body made of impact modified nylon
- Superior chemical, corrosion and temperature resistant properties.
- Comes with vinyl-coated steel cable or nonconductive nylon cable
- 6 lock holes accommodate most padlock shackles and hasps
- Body dimensions: 4" diameter x 1 3/4" deep
- Cable dimensions: 1/16" outside diameter x 8' length

Catalog #	Description	Price Each
50940	Mini Cable Lockout w/ Steel Cable	\$41.74
51442	Mini Cable Lockout w/ Nylon Cable	\$41.74



Original Cable Lockout

- Brady's original cable lockout
- Body made of impact modified nylon, available in red, blue or yellow
- Comes with 6' galvanized steel cable (1/8" outside diameter)

Cable Lockout Device with 6 ft. cable

Catalog #	Color	Price Each
65318	Red	\$43.02
45191	Blue	\$43.02
45192	Yellow	\$43.02

Additional Cables

Catalog #	Description	Price Each
65319	8 ft. cable	\$11.83
65320	10 ft. cable	\$13.83

Other cable lengths available upon request.



PRINZING Economy Cable Lockout

- Unique lockout device accepts up to six 9/32" diameter padlocks
- Cable Diameter 3/16" outside diameter
- Plastic-coated steel cable comes in two lengths: 6' and 10'

Catalog #	Description	Price Each
CABLO	Cable Lockout Device w/6'cable	\$27.02
CABLO-10	Cable Lockout Device w/10'cable	\$30.80



PRINZING Cable Lockout Kit

- Cable lockout kit with handy carrying case
- Components
 - 2 - Cable Lockout Devices (CABLO)
 - 2 - Blue Prinzing Padlocks (LC041-BU)
 - 1 - 1" Steel Lockout Hasp (T218)
 - 2 - Eng/Sp Lockout Tags w/ Ties
 - 1 - Rugged Polyethylene Carrying Case (7"H x 12"W x 5"D)

Catalog #	Description	Price Each
LK520B	Cable Lockout Kit	\$99.85



PRINZING Chain Lockout Kit

- An inexpensive way to lockout misc. applications
- Components
 - 3 - 1 1/2" Steel Lockout Hasp (T220)
 - 3 - Padlocks (LC044-RD)
 - 3 - Lockout Tags w/Ties
 - 1 - 48" Chain
 - 1 - Durable Carrying Case (7"H x 12"W x 5"D)

Catalog #	Description	Price Each
LK041R	Single Lockout Kit	\$111.74
LK042R	Double Lockout Kit*	\$117.00

*Same as LK041R plus an extra chain

Valve Lockouts

www.BradyID.com/lockouttagout

Universal Valve Lockout

Lock Out All Types Of Valves With A Single Device!

- Versatile, rugged, easy to use, lightweight
- Made of industrial-grade steel and nylon for extra impact and chemical resistance
- New open-ended clamp fits over closed rings, wide handles
- Can also be used to lock out large levers, T-handles and other hard-to-secure mechanical devices
- Cable attachment offers choice of 1/8" nonconductive nylon or rustproof sheathed metal cable
- Small UVLO: for use on handle widths up to 1" (max handle thickness of 0.6")
- Large UVLO: for use on handle widths up to 1.6" (max handle thickness of 1.1")
- Patent No. 5,415,017 and 7,207,198



No need for multiple types and sizes of lockouts
– now one device does it all!

Universal Valve Lockout - Complete Sets

Catalog #	Description	Price Each
51394	Small UVLO w/ 8' Sheathed Cable Attachment & Blocking Arm	\$81.38
51390	Small UVLO w/ 8' Nylon Cable Attachment & Blocking Arm	\$83.83
51392	Large UVLO w/ 8' Sheathed Cable Attachment & Blocking Arm	\$87.54
51388	Large UVLO w/ 8' Nylon Cable Attachment & Blocking Arm	\$84.99

Universal Valve Lockout - Individual Components

Catalog #	Description	Price Each
50924	Small UVLO Base Clamping Unit	\$43.12
50899	Large UVLO Base Clamping Unit	\$49.29
65402	Small Blocking Arm	\$26.08
65403	Large Blocking Arm	\$28.72
51395	Cable Attachment w/ 8-ft Sheathed Cable	\$19.69
50932	Cable Attachment w/ 8-ft Nylon Cable	\$22.13

Other cable lengths also available.



Use blocking arm to lock out quarter-turn ball valves.



Clamp attaches to butterfly handles, preventing trigger handle from being squeezed. Valve cannot be repositioned!



Use two blocking arms to lock out 3-, 4- or 5-way valves, or to lock valves in the "on", "off", or "throttled" position for operational control.



Use cable attachment to lock out gate valves.

Plug Valve Lockout

- Four Sizes to Fit Most 1" to 8" Diameter Manually-Actuated Plug Valves
- Effective Fit for Difficult-to-Secure Plug Valves
- Durable and Tamper-Resistant
- Service Temperatures from -25°F to 200°F
- Compact in Size and Easy to Use

Catalog #	Description	Price Each
113231	Plug Valve L/O for up to 7/8" Stem Dia	\$21.41
113232	Plug Valve L/O for 1 5/16" - 1 3/8" Stem Dia	\$21.41
113233	Plug Valve L/O for 1 3/4" - 2 1/8" Stem Dia	\$32.12
113234	Plug Valve L/O for 2 3/16" - 2 1/2" Stem Dia	\$32.12



With Brady's Plug Valve Lockout, you can easily and effectively secure manual plug valves to OSHA-compliant standards.

Adjustable Gate Valve Lockout

- Versatile lockout adjusts to fit 1" to 6 1/2" valve handles, replacing 3 conventional gate valve lockouts
- Durable polypropylene is resistant to temperature changes from -13°F to 194°F
- Compact for easy carrying and storage
- Comes with danger labels in English, Spanish and French

Catalog #	Description	Price Each
64057	Adjustable Gate Valve Lockout	\$35.01



Gate Valve Lockouts

- Made of rugged injection-molded polypropylene
- Service temperatures from -25°F to 200°F
- Unique knockout center accommodates OS&Y or "rising stem" valves
- Available in 5 sizes and 4 colors
- Accepts locks with shackles up to 3/8" in diameter
- Supplied with danger labels in English, Spanish and French

Valve Handle Diameter	Catalog #				Price Each
	Red	Yellow	Green	Blue	
1" - 2 1/2"	65560	65590	65595	65585	\$17.21
2 1/2" - 5"	65561	65591	65596	65586	\$28.86
5" - 6 1/2"	65562	65592	65597	65587	\$34.56
6 1/2" - 10"	65563	65593	65598	65588	\$43.28
10" - 13"	65564	65594	65599	65589	\$83.96



Standard Ball Valve Lockout

- Easy to use, single-piece design locks quarter-turn ball valves in OFF position
- Two sizes fit most valves up to 3"
- 65692, 65669 and 65693 are made of powder-coated steel
- 65666 is made of super-tough nylon (service temp -40° to 248° F)

Catalog #	Max Shackle Diameter	Valve Size/ Pipe Diameter	Max Handle Width (inches)	Max Handle Thickness (inches)	Price Each
65666	9/32"	1/4" - 1"	1 1/2"	3/4"	\$25.20
65692	3/8"	1/4" - 1"	1 1/2"	3/4"	\$28.50
65669	9/32"	1 1/4" - 3"	2 1/10"	1 1/4"	\$41.42
65693	3/8"	1 1/4" - 3"	1 9/10"	1 1/4"	\$41.86



PRINZING Ball Valve Lockout

- Made from ultra-tuff polypropylene
- Small lockout (BS07A) locks out pipes 1/2" to 2 1/2" in diameter
- Small lockout can also be used to lock valves OPEN on pipes from 1/2" to 1 1/4" in diameter
- Large lockout (BS08A) locks out pipes 2" to 8" in diameter
- Available in 4 colors



Description	Red	Blue	Green	Yellow	Price Each
Small Ball Valve Lockout	BS07A	BS07A-BU	BS07A-GN	BS07A-YW	\$27.02
Large Ball Valve Lockout	BS08A	BS08A-BU	BS08A-GN	BS08A-YW	\$54.06

Circuit Breaker Lockouts

www.BradyID.com/lockouttagout

EZ Panel Loc™ System

- Works on wide range of breakers, including single- and multi-pole configurations
 - Makes use of unique lock rail system
 - Allows panel door to be closed even when lockouts are in place
 - Accommodates multiple locks, facilitating group lockout activity without hasps
 - Keeps weight off the breakers, protecting delicate electrical components from damage
 - Positions locks and tags outside the panel, making sure lockout activity is clearly visible to anyone in the area
 - Patent No. 6,727,441
- (Not recommended for use with multilock hasps)

How EZ Panel Loc System Works



Lockout device is unlocked by inserting and turning the black plastic key.



1 Peel liner off bottom of lock rail, exposing super-bond adhesive. Permanently affix to any location on the panel. No drilling required!



2 Attach the lockout device to the breaker and snap into locked position.



3 Pass plastic key through lock rail and attach lock, preventing key from sliding down cable and opening lockout device.



4 For group lockouts, run key through multiple loops in lock rail and apply locks. No hasps required!
(Not recommended for use with multilock hasps)



5 Low-profile lockouts allow panel doors to be closed on most breaker panels.

Covers Most 120V – 277V Breakers!

- The EZ Panel Loc™ System includes two types of lockout devices, accommodating an exceptionally wide range of breaker models.



SNAP-ON

For use on Square D NQO and other breakers that have a hole in the switch tongue. Just align pins with hole and snap closed. Pins prevent switch from being thrown.

CLAMP-ON


For use on breakers that do not have a hole in the switch tongue, including multipole breakers with tie-bars. Turn thumbscrew to clamp lockout securely onto switch, then snap the cover closed to prevent thumbwheel from being loosened.



EZ Panel Loc™ System

“No Shackle” EZ Panel Locks

The EZ Panel Loc system can be used with most padlocks. A shackle-less padlock designed specifically for use with the EZ Panel Loc key is also available. This is especially useful when lockout devices will be kept at the panel in accordance with NEC regulations (see below). Everything you need to lockout breakers is kept conveniently right at the point of need!



Did You Know?

“The provisions for locking or adding a lock to the disconnecting means shall be permanently installed on or at the switch or circuit breaker used as the disconnecting means.”

- NEC 2002, Article 430.102(B) Motor



Spacing Gasket

For low profile panels, a spacing gasket can be installed, pushing out the panel frame and adding an additional 3/8" of clearance between the panel surface and the door. Self-adhesive backing makes installation quick and easy. Dimensions: 3/8"D, 1"W, 15'L.


Catalog #	Description	Price
89256	EZ Panel Loc™ Spacing Gasket	\$30.68




Technical Information

- Lockout devices constructed of high-impact Isoplast polymers
- Cables are 2-ft. in length
- Lock rails made of durable isoplast polymers with acrylic adhesive backing
- Lock rails available in 4" or 8" lengths (containing 7 or 15 lock loops)
- Patent No. 6,727,441

Snap On



Clamp On



	Outer Dimensions (in.)			Switch Clearance (in.)	
	A	B	C	D	E
Snap-On Style	0.90"	1.88"	0.74"	0.40"	0.35"
Clamp-On Style	0.95"	2.56"	0.74"	0.35"	0.42"

Description	1 Per Pkg	Price	6 Per Pkg	Price
Snap-On Lockout Device	51252	\$24.49	65815	\$130.02
Clamp-On Lockout Device	51254	\$24.49	65810	\$130.02
4" Lock Rail	51256	\$8.34	65814	\$30.68
8" Lock Rail	51258	\$10.98	51260	\$45.35
No-Shackle Lock	59505	\$14.67	51263	\$78.25
Spacing Gasket	89256	\$30.68	-	-

Circuit Breaker Lockouts

www.BradyID.com/lockouttagout

120V Snap-On Breaker Lockout

- Designed for 120V breakers that have holes in the switch tongue
- Quick and easy – just snap in place and apply lock!
- Dual cavities accommodate different size switch tongues
- Accepts locks shackles up to 3/32" in diameter
- Dimensions: 0.83"H x 0.35"W x 2.15"L



Catalog #	Description	Qty	Price
65387	120V Snap-On Circuit Breaker Lockout	1/pkg	\$5.16
65688	120V Snap-On Breaker Lockouts	6/pkg	\$27.86

Clamp-On Breaker Lockouts

- Extremely versatile – works on wide range of single-pole and internal-trip multi-pole breakers!
- Two sizes, one for 120/277V breakers and one for 480/600V breakers
- Made of rugged polypropylene and impact modified nylon
- Use thumbscrew to clamp lockout securely onto switch tongue, then pull cover over thumbscrew and lock in place to prevent clamp from being loosened
- New blade design provides tighter grip with less torque on thumb screw
- Detachable cleats (included) expand the range of applicable breakers
- Accepts locks shackles up to 3/32" in diameter



The Brady Clamp-On Circuit Breaker Lockout works on an extremely wide range of breakers.

Catalog #	Description	Qty	Price
65396	120/277V Clamp-On Breaker Lockout	1/pkg	\$10.36
65965	120/277V Clamp-On Breaker Lockouts	6/pkg	\$56.93
65397	480/600V Clamp-On Breaker Lockout	1/pkg	\$11.64
65966	480/600V Clamp-On Breaker Lockouts	6/pkg	\$62.83

Extra Cleats for Clamp-On Breaker Lockouts

- Use in conjunction with clamp-on breaker lockouts (sold above)
- Easily clips onto the bottom of the lockout body
- Assures positive restraint for breakers with long, sliding switch throws

Catalog #	Description	Qty	Price
65404	Cleats For 120/277V Lockout	6/pkg	\$6.48
65406	Cleats For 480/600V Lockout	6/pkg	\$8.41



Step 1



Step 2



Step 3

Universal Multi-Pole Breaker Lockout

- Single device works with most major multi-pole breakers that employ a tie-bar
- Made of durable impact-modified nylon
- Compatible with GE, ITE, Sylvania, Challenger, Bryant, Westinghouse, General Switch Co., and more!
- Use thumbscrew to clamp lockout securely over tie bar, then insert lock to prevent clamp from being loosened
- Patent No. 5,300,740

Catalog #	Description	Qty	Price
66321	Universal Multi-Pole Breaker Lockout	1/pkg	\$10.36
66320	Universal Multi-Pole Breaker Lockouts	6/pkg	\$56.93



Universal Multi-Pole Lockout works with most two or three pole breakers utilizing a tie-bar.

Circuit Breaker Lockouts

www.BradyID.com/lockouttagout

Oversized Clamp On Breaker Lockout

- Oversized 480/600V frame lockout fits breaker switches up to 2 1/4" wide and 7/8" thick
- Made of durable polypropylene and glass filled-impact-modified nylon
- New blade design gets better grip, works on even more breaker models!
- Patent No. 5,500,495



Catalog #	Description	Qty	Price
65329	Oversized Breaker Lockout	1/pkg	\$16.02
65321	Oversized Breaker Lockout	6/pkg	\$75.80

480-600V Breaker Blocker

- Perfect for locking out oversized and irregularly shaped switches
- Self-adhesive backed rails are permanently installed into an electrical panel – simply clean panel surface and adhere – no drilling required!
- Blocking bars (red and green) are 7 1/2" long
- Red blocking bar indicates locked off, green bar indicates locked on



Breaker Blocker Kit

Catalog #	Description	Qty	Price
90891	Breaker Block Kit	1/pkg	\$25.34

Kit includes 2 yellow mounting rails, 1 red blocking bar, 1 green blocking bar and 3 alcohol wipes.


Breaker Blocker Components

Catalog #	Description	Qty	Price
90892	7.6" Red Blocking Bar	5/pack	\$18.98
90893	7.6" Green Blocking Bar	5/pack	\$18.98
51264	4" Yellow Mounting Rails	2/pack	\$20.27
51265	Blocking Bar Holder	5/pack	\$24.07



Not Sure Which Circuit Breaker Lockout To Use?

Check out Brady's Circuit Breaker Lockout Reference Guide. We've tested over 750 makes and models of breakers, including popular brands such as Allen Bradley, ABB, Cutler Hammer, General Electric, Siemens, Square D and more! The Reference Guide makes it easy to find the right lockout device for the breakers you use. Download the reference guide from www.bradyid.com/lockouttagout, or call Brady customer service at 888-272-3946 and order publication MS483783. **AND BEST OF ALL, IT'S FREE!**



Circuit Breaker Lockouts

www.BradyID.com/lockouttagout

Miniature Circuit Breaker Lockouts



Tie-Bar (TBLO)



Pin-Out Standard (POS)



Pin-In Standard (PIS)



Pin-Out Wide (POW)

4 Different types:	POS	Pin Out Standard
	PIS	Pin In Standard
	POW	Pin Out Wide
	TBLO	Tie Bar Lockout

- A safe and effective method for locking out miniature circuit breakers, commonly used in European and Asian equipment
- Miniature Breaker Lockouts require NO TOOLS to install! The Lockout easily installs with the aid of a push button. The Tie Bar Style Lockout has a convenient thumb wheel for quick application.
- Available for single and multi-pole breakers
- Recommended to lock with lightweight Brady Safety padlocks (see page 199) or other padlocks, the lockouts can take padlocks with a shackle diameter up to 3/32"
- Material: Glass-filled nylon
- Available in 1 or 6 packs

Catalog #	Type	Qty	Price
90844	POS	1	\$12.29
90845	POS	6	\$67.81
90847	PIS	1	\$12.29
90848	PIS	6	\$67.81
90850	POW	1	\$12.29
90851	POW	6	\$67.81
90853	TBLO	1	\$12.29
90854	TBLO	6	\$67.81

Breaker Compatibility Chart

Brand	Poles	Model No.	Catalog #/1/pkg.	Type	Brand	Poles	Model No.	Catalog # 1/pkg.	Type
ABB	1	S222	90844	POS	Legrand	4	01980	90844	TBLO
ABB	1	F374	90844	POS	Legrand	2	04302	90847	PIS
ABB	1	S251, S261, S263	90844	POS	Legrand	3	06469	90847	PIS
ABB	1	S272, S253	90844	POS	Legrand	1	01908	90844	POS
ABB	3	S253	90844	POS	Merlin Gerin	3	C80A	90850/90853	TBLO/POW
AEG	2	E82S	90847	PIS	Merlin Gerin	2	B100A	90850/90853	TBLO/POW
Allen-Bradley	1,2,3	1492-CB1, 2, 3	90844	POS	Merlin Gerin	1	C60N	90844	POS
Buschmat	1	S46	90844	POS	Merlin Gerin	1	C32N	90844	POS
Clipsal	1	4CB116	90844	POS	Merlin Gerin	2	C60N	90844	POS
Clipsal	3	4CB320	90844	POS	Merlin Gerin	4	C60N	90844	POS
E-T-A	1	911225	90847	PIS	Merlin Gerin	3	C32N	90844	POS
E-T-A	2	911220G	90844	POS	Merlin Gerin	3	C45AD	90844	POS
FAZ	4	C16	90844	POS	Proteus	1	C16	90844	POS
FAZ	1	C16	90844	POS	Proteus	1	C6	90844	POS
GE Vynckier	3	Series E	90847	PIS	Proteus	3	C6	90844	POS
GE Vynckier	3	Series G	90847	PIS	Siemens 17U	2	5SQ12	90853	TBLO
GE Vynckier	4	Series E	90847	PIS	Siemens 17U	3	5SQ13	90853	TBLO
GE Vynckier	1	Series G	90847	PIS	Siemens 17U	4	5SQ16	90853	TBLO
GE Vynckier 16A	2	Series E	90847	PIS	Siemens 17U	1	5SQ11	90850	POW
GE Vynckier C16, 16A	1	Series E	90847	PIS	Siemens C10	1	5SX1	90850	POW
Hager	3	453717	90844	POS	Siemens C32	2	5SX1-2	90853	TBLO
Hager	2	MW216A	90844	POS	Siemens C70	3	5SX13	90853	TBLO
Hager	4	MW620A	90844	POS	Siemens L20A	2	5SN2-2	90853	TBLO
Kapp	1	LS68	90844	PIS	Sursum	3	EA53	90847	PIS
Legrand	2	01935	90844	TBLO	Wylex	2	WRS40/2	90844	POS
Legrand	3	01980	90844	TBLO					

View full compatibility chart at www.BradyID.com/lockouttagout.

3-In-1 Electrical Plug Lockout

- Accommodates high and low-voltage plugs up to 3" in diameter and 5½" in length
- 2 sliding top lids can be used individually or together to accommodate small, medium and large-diameter cords up to 1¼"
- Made of bright yellow thermoplastic
- Available with English or English/Spanish instruction labels

Catalog #	Description	Price
PL023	3-in-1 Plug Lockout - English	\$16.10
PL023-BI	3-in-1 Plug Lockout - English/Spanish	\$16.10



Brady Electrical Plug Lockouts

- Plug lockouts prevent electrical plugs from being inserted into a wall outlet. Use when plug will not remain under the exclusive control of the person performing service or maintenance
- Made of rugged polypropylene
- Small 110V plug lockout: 2"H x 2"D x 3½"W with ½" diameter hole for cable
- Large 220/500V plug lockout: 3¼"H x 3¼"D x 7"W with 1" diameter hole for cable

Catalog #	Description	Price
65674	Small 110V Plugout	\$15.44
65675	Large 220/500V Plugout	\$18.69




Brady Plug Lockouts

Electrical/Pneumatic Plug Lockout

- Accommodates a large variety of electrical plugs up to 3½" in diameter and 5" in length as well as male air hose connectors
- Holes accommodate electrical cord or "necked down" pneumatic male fittings commonly attached to compressed air hose
- Works on 110V, 220V & 550V plugs
- Made of Polystyrene material

Catalog #	Description	Price
PL027E	Electrical/Pneumatic Plug LO	\$19.02



Hubbell Plugout™

- Two sizes available to fit most heavy industrial plug applications
- Small version accepts plugs with maximum 2¾" diameter and 4¾" length with 1" cord
- Large version accepts plugs with maximum 4½" diameter and 10¾" length with 1½" cord
- Standard package: one device

Catalog #	Description	Price
65695	Small Plugout™	\$29.44
65968	Large Plugout™	\$36.12



Stopower™ Plug Lockouts

- Ideal for office equipment and other frequently locked out cords
- For use on 2 or 3 pronged polarized plugs
- Cord cannot be plugged in with Stopower™ in place
- Device cannot be removed without a key

Catalog #	Description	Price
65673	Red - 1 device/pkg.	\$19.73

To order multiple Stopower Plug Lockouts that are keyed alike, use catalog #98209



Electrical Lockouts

www.BradyID.com/lockouttagout

Push Button Lockouts



Push Button Cover IEC 30.5 mm (104602)



Emergency Stop Cover IEC 22.5mm (104601)



Emergency Stop Cover NEMA 30.5mm (104600)



Push Button Cover NEMA 22.5mm (104603)

- Guard against unauthorized operation or accidental activation.
- Two sizes to accommodate standard NEMA 30.5 mm and IEC 22.5 mm buttons.
- Emergency Stop Safety Covers:
 - Permanently install over push/pull or twist-release emergency stops.
 - Durable metal bar locks button in the depressed (off) position when lock shackle is inserted
- Push Button Safety Covers:
 - 104602: Clear Lexan hinged cover completely covers button, preventing access. White legend plate included.
 - 104603: Clear Lexan & metal hinged cover completely covers button preventing access.

Catalog #	Description	Price
104600	Emergency Stop Safety Covers - NEMA 30.5 mm	\$60.41
104601	Emergency Stop Safety Covers - IEC 22.5 mm	\$68.82
104602	Push Button Safety Cover - NEMA 30.5 mm	\$60.41
104603	Push Button Safety Cover - IEC 22.5 mm	\$68.82

Wall Switch Lockouts



- Device may be used with most wall-mounted switches
- Easy to install using existing screws
- High visibility red color
- Locks switch in "on" or "off" position
- Lock not included

Catalog #	Quantity	Price
65392	1/Pkg.	\$11.27
65696	6/Pkg.	\$61.23



- Clear plastic lockout uses existing wall plate screws to mount
- Patented non-hinge design
- Made of strong, clear polycarbonate
- Lock not included

Catalog #	Description	Price
WSLO	Wall Switch Lockout	\$8.14


Fuse Lockout Devices



- Unique locking mechanism prevents device from being accidentally removed from fuse block
- Available in two sizes for most commonly used fuses

Catalog #	Size	Quantity	Price
65750	$\frac{13}{32}$ "	6/Pkg.	\$61.82
65751	$\frac{9}{16}$ "	6/Pkg.	\$63.64

Fuse Blockout Devices



- Block out $\frac{1}{4}$ " to $\frac{1}{16}$ " and blade type fuses
- Use these highly visible devices in conjunction with Brady Lockout Tags (sold separately on page 194) to comply with OSHA's Lockout/Tagout Standard


Catalog #	Description	Quantity	Price
65690	$\frac{1}{4}$ ", $\frac{9}{32}$ ", $\frac{13}{32}$ " & $\frac{9}{16}$ " fuses	6/Pkg.	\$28.08
65691	$\frac{13}{16}$ ", $1\frac{1}{16}$ " & blade type fuses	6/Pkg.	\$56.12

Fuse Puller with Testlite

- Handy pocket-sized tool provides maximum safety when pulling cartridge fuses or checking electrical connections
- One end is a fuse puller, opposite end has test prods that fit both parallel and tandem slot receptacles
- Use on fuses up to 100A/250V. and 60A/600V.

Safe-T-Grip® Fuse Pullers

- Provides maximum convenience when removing or replacing cartridge fuses
- Notched handles for no-slip grip
- Clearly marked amperage ranges
- Exceeds MIL specifications



Fuse Puller with Testlite (A) and Safe-T-Grip® Fuse Pullers (B, C)

Catalog #	Description	Price
65281	(A) 8" long	\$37.57
65279	(B) For 9/32"-7/2" diameter fuses: 5" long	\$9.89
65280	(C) For 0-100A, 250V & 600V: 7 1/2" long	\$14.84

AC Sensor

- Selected by OSHA Electrical Technical Equipment Committee as the only instrument of its type for use by OSHA compliance officers to identify and cite electrical hazards of 50 - 1000 volts AC
- Uses AAA battery
- CAT IV rated and UL Listed
- Patent #5,103,165

Catalog #	Description	Price
65269	AC Sensor	\$45.60



E-Z Check® Plus GFI Circuit Tester

- Checks for the following conditions: correct wiring, open ground, reverse polarity, open hot, open neutral, hot on neutral, hot and ground reversed with open hot, and ground fault interruption

Catalog #	Description	Price
65273	E-Z Check® Plus GFI Circuit Tester	\$56.85



Gas & Air Line Lockouts

www.BradyID.com/lockouttagout

Pneumatic Quick-Disconnect Lockout



- Isolates pneumatic energy without the expense and inconvenience of installing in-line lockout valves
- Device is applied to the male fitting, isolating equipment from all compressed air sources
- Accommodates the majority of 1/4", 1/8", 1/2" male fittings
- Hole in center of device allows for permanent storage on an air hose and a loop on the side can be used to hang the hose and lockout device
- Lockout using a padlock with 1/4" or 9/32" shackle

Catalog #	Qty	Price
64221	1/pkg	\$22.92
65645	6/pkg	\$118.23

SMC Air Line Regulator Lockout



- Enables regulator to be locked in the on, off or throttled position
- Easy installation: remove snap cap, install lockout on regulator rod, snap replacement cap on regulator.
- Comes with lockout, cap and allen wrench

Catalog #	Description	Price
64539	Lockout for Miniature SMC Models AR2000 / NAR2000	\$24.71
64540	Lockout for Intermediate SMC Models AR3000 / NAR3000	\$24.71



Want to learn more about Lockout/Tagout?

Visit www.BradyID.com/lockouttagout to:

- Download the 5 Steps to an Effective Lockout/Tagout Program Whitepaper
- Enhance your safety program with eLearning online training courses
- View Brady's full line of lockout/tagout product solutions



Gas & Air Line Lockouts


www.BradyID.com/lockouttagout



PRINZING Cylinder Tank Lockout

- Used to lockout cylinder tanks, including propane tanks on fork trucks and stand alone propane tanks
- Apply with ease to prevent access to the valve handle
- Designed to fit in tight spaces
- Valve stem hole is 1.25" in diameter
- Made of rugged polystyrene plastic

Catalog #	Description	Price
SD02M	Cylinder Tank Lockout	\$13.46



PRINZING Gas Cylinder Lockout

- Prevents access to the main cylinder valve
- No need to match your lockout device to varying diameters and threads of cylinder caps
- Accommodates neck rings up to 3 1/2" diameter
- Installs in seconds to save time

Catalog #	Description	Price
LM023E	Gas Cylinder Lockout	\$16.57



Snap Cap™ Gas Cylinder Lockout

- Designed to fit most North American high and low pressure gas cylinders
- SNAP CAP cylinder safety device meets DOT standards
- The SNAP CAP denies access to the main cylinder control and regulator attachment
- Welded steel construction and powder coated for many years of use

Catalog #	Description	Price
90496	6.5" x 3-1/8" x 11 UN, High Pressure Fine Thread	\$128.26
95137	6.5" x 3-1/2" x 11 UN, Low Pressure Fine Thread	\$128.26
95138	6.5" x 3-1/8" x 11 UN, High Pressure Coarse Thread	\$128.26
95139	6.5" x 3-1/2" x 11 UN, Low Pressure Coarse Thread	\$128.26

Energy Source Identification

www.BradyID.com/lockouttagout

Polyester Labels


- Made of self-sticking high-performance polyester (B-302)



3½ x 5 - 86246



3½ x 5 - 86216



5" x 3½" - 86240



3½ x 5 - 86199



3½ x 5 - 86245




3½ x 5 - 86204


Description	Size	Quantity	Price
Polyester Labels	3½" x 5"	(5/pkg)	\$10.93

Energy Source ID Requirements


- OSHA 1910.333(e) and (f) require that all disconnecting means show the magnitude and shall be legibly marked to indicate the purpose, unless located and arranged so the purpose is evident.
- ANSI Z244.1-2003, Control of Hazardous Energy, states that all energy isolating devices should be adequately labeled or marked unless they are located so that their purpose is clearly evident. Identification shall include the following:
 - Machine, equipment, process supplied
 - Energy type and magnitude



7 x 10 - 60179



7 x 10 - 60180



3½ x 5 - 50276

Vinyl Labels

- Made of self-sticking vinyl (B-946)

Description	Size	Quantity	Price
Vinyl Labels	7" x 10"	1/pkg.	\$8.10

Write-On Energy Source Label


- Constructed of B-933 vinyl
- Accepts writing in pen or marker
- Overlaminates available for added protection

Part No.	Description	Qty	Price
50276	Write-On Energy Source Labels	10/Pack	\$21.77
58706	Overlaminates (3½" x 5½")	50/Pack	\$24.75

Self-Laminating Tag

- Constructed of durable B-851 polyester with 1-mm polyester overlay on front side
- Standard package: 10 tags and nylon fasteners
- Tag dimensions: 5¾" x 3" or 7" x 4"

Catalog #	Description	Size	Quantity	Price
50194	Self-Laminating Tags	5¾" x 3"	10/pkg.	\$22.56



Front Side

Back Side

May We Also Suggest:

Industrial Label Printing Systems

- Create your own signs, pipe marker and labels using Brady's make-it-yourself printing system
- Ideal for making one-of-a-kind labels for your lockout compliance program
- Make energy source ID labels, equipment ID placards, panel labels, operator control messages and warning labels.



BBP®31 Sign & Label Printer (page 136)



BMP®71 Label Printer (page 108)

Lockout Identification

www.BradyID.com/lockouttagout


Lockout Safety Signs

- Available in Premium Fiberglass (B-120) and BradyTuff™ Plastic (B401)
- Size: 7" x 10"

Material	Price
Fiberglass	\$13.19
Plastic	\$9.81



Fiberglass - 65571
Plastic - 22909



Plastic - 22931

Lockout Safety Labels

- Made from self-sticking high-performance polyester (B-302)



2¼ x 4½ -88302



2¼ x 4½ -88303



3½ x 5 - 86248

Size	Quantity	Price
2¼" x 4½"	1/pkg.	\$1.58
3½" x 5"	5/pkg.	\$10.93




3½ x 5 - 86250

Magnetic Signs

- Made of flexible magnetic vinyl
- Two sizes available

Size	Price
5" x 3½"	\$12.99
7" x 5"	\$15.27



5 x 3½ - 66008
7 x 5 - 66009



5 x 3½ - 66004
7 x 5 - 66005



5 x 3½ - 66006
7 x 5 - 66007

Rigid Plastic Signs

- Made of BradyTuff™ plastic (B-401)
- Size: 7" x 10"



7 x 10 - 50270



7 x 10 - 50269

Size	Quantity	Price
7" x 10"	1/pkg.	\$9.81

Floor Stands



PRINZING Floor Stand

- Made from rugged polyethylene, resists most chemicals
- Message printed on front and back
- Dimensions: 20" high x 12" wide

Catalog #	Description	Price
SF647E	Lockout Floor Stand	\$28.71



(side 1) (side 2)

Two-In-One Floor Stand

- Made of lightweight corrugated polypropylene (B-836)
- Printed on both sides - inside and out - offering two stands for the price of one
- Dimensions: 20" high x 12" wide

Catalog #	Description	Price
92289	Two-In-One Floor Stand	\$43.12

Barricades



Striped Warning Posts & Chain

- Chain and base/top of post made of polyethylene; post made of polystyrene
- Posts: black and yellow (4" bands), Chain: yellow
- Post dimensions: 41" height x 3" diameter (base 16" in diameter)
- Chain length: 100 feet (2" links) • Indoor use only

Catalog #	Description	Price
92122	Striped Warning Post (6/box)	\$105.46
78238	Chain (100 feet)	\$217.69



Bradystripe™ Temporary Barricade Tape

- Made of black/yellow striped vinyl (B-933)
- Adhesive backing sticks to most wood, metal or concrete walls for easy application
- Removes cleanly and easily with no adhesive residue
- Tears apart easily - perforated every 14" • Roll size: 2" wide x 100' long

Catalog #	Legend	Price
91230	Caution / Do Not Enter	\$55.74
91231	Caution / Men Working	\$55.74

Lockout/Tagout

Training & Awareness Aids

www.BradyID.com/lockouttagout

Lockout/Tagout

Lockout/Tagout Handbook


- 16-page training booklet with quiz instructs workers how to protect themselves from hazardous energy

Catalog #	Description	Quantity	Price
66219	Lockout/Tagout Handbook	10/pkg.	\$29.08
63004	Spanish-language Handbook	10/pkg.	\$29.08



Lockout Safety Training Booklet

- 16-page training booklet covers the basics of lockout/tagout safety



Catalog #	Description	Quantity	Price
2112-TEN	Lockout Safety	10/pkg.	\$12.88
2112	Lockout Safety	25/pkg.	\$33.33
2112SP-TEN	Spanish-language version	10/pkg.	\$12.88
2112SP	Spanish-language version	25/pkg.	\$33.33

Wallet Safety Cards

- Wallet size card contains important reminders for lockout safety
- Available in English or English/Spanish
- Package of 10



Catalog #	Description	Quantity	Price
LOSC13	English Wallet Card	10/pkg.	\$11.53
LOSC13BI	English/Spanish Wallet Card	10/pkg.	\$12.50

PRINZING Lockout Safety Poster

- Training poster reinforces your energy control program
- 18"H x 24"W, laminated on both sides

Catalog #	Description	Price
LOSP8	Lockout Safety Poster	\$25.89
LOSP8SP	Spanish-language version	\$25.89



Hard Hat Labels

- Made of B-946 indoor/outdoor vinyl
- Size: 2" diameter
- Four labels per card

Catalog #	Description	Price
42248	Hard Hat Label - Lockout/Tagout Trained	\$2.79
50193	Hard Hat Label - Lockout/Tagout Authorized	\$2.79



Cat. No. 42248



Cat. No. 50193

LockoutPRO™ Enterprise software also provides training tools, including an online training module that allows employees to undertake training at their own computer. See pages 229.



OSHA Training Requirements:

- Those who will perform servicing or maintenance (authorized employees) must be trained to:
 - Recognize hazardous energy sources and understand the energy type and magnitude
 - Identify and properly operate the applicable energy-isolating devices
 - Safely apply and remove lockout/tagout devices
- Those who operate the machinery or work in the area where LOTO is performed (affected employees) must be trained to:
 - Recognize when lockout/tagout activities are in progress
 - Understand the purpose of the energy control program and the importance of not tampering with lockout/tagout devices when encountered in the workplace
- Additional training is required when using tagout instead of lockout. See Section (C)(7)(ii) in the 1910.147 standard.
- Employers must document when training took place, who attended, and the topics covered.
- Employees must be retrained under the following situations:
 - Employee assigned to new job
 - Change made to energy control policies or procedures
 - Machinery installed or modified, presenting a new hazard
 - Whenever the employer has reason to believe that there are problems with the employee's understanding or use of the procedures
- Authorized employees must undergo an annual review to ensure they fully understand their responsibilities under the program=

Lockout/Tagout e-Learning Courses

Train your employees on lockout compliance with Brady's new online training courses. The courses feature interactive features, real-life application scenarios and quizzes to facilitate learning and remembering. Employees can access the courses online from your facility, which eliminates the costs of off-site training. Certificate available upon completion.

Only Available at www.BradyID.com

Catalog #	Description	Price
142253	LOTO For Authorized Workers (approx. length 1hr 30min)	\$29.95
142254	LOTO For Corporate Safety Leader (approx. length 1hr)	\$29.95
142255	e-Learning Bundle: (1) LOTO For Auth Worker and (1) LOTO for Corp Safety Leader	\$49.95



Lockout/Tagout Training: A Program for Employees

Train employees to protect themselves and others during machine servicing and maintenance. This program shows how to recognize all potential hazards and handle them safely. Includes:

- Live action 13 minute, DVD video
- Instructors guidebook with quizzes, 24 pages
- 10 employee handbooks
- 10 certificate of completion wallet cards
- Training log book
- Full-color poster
- Sample tag & warning decal
- Carrying case


Catalog #	Description	Quantity	Price
104275	Complete Kit - DVD version - English	1	\$444.20
104216	Complete Kit - DVD version - Spanish	1	\$477.93



Lockout For Life

- Learn from other workers' tragic mistakes. This motivational video presents six real-life dramatizations of actual lockout accidents and analyzes how they could have been prevented
- Suitable for new and experienced employees
- Run time: 19 minutes (VHS or DVD formats)

Catalog #	Description	Price
66255	Lockout For Life VHS video (includes 10 booklets)	\$547.39
51793	Lockout For Life DVD English/Spanish (includes 10 English booklets)	\$637.55
51544	Lockout For Life VHS video (Spanish)	\$547.39
65555	Additional booklets (10/pkg.)	\$29.51



LOTO for Authorized & Affected Personnel

- Provides a comprehensive introduction to the key components of an effective LOTO program
- Run time: 17 minutes (DVD format)
- Comes with reproducible quiz and certificate
- Spanish language video also available (quiz and certificate in English only)

Catalog #	Description	Price
51454	LOTO For Authorized & Affected Personnel DVD (English)	\$225.39
51455	LOTO For Authorized & Affected Personnel DVD (Spanish)	\$225.39



Energy Control Procedures

www.BradyID.com/lockouttagout

Post procedures near the point of need so they are easy to find and readily accessible.

Lockout/Tagout



Lockout Procedure Station

- Silk-screened backboard made from durable polystyrene
- Includes pre-drilled holes and hardware for wall mounting
- 3-ring, 1.5" binder made from 55 gauge polyethylene
- Backboard dimensions: 20"H x 14"W x 4.5"D

Catalog #	Description	Price
LOSP22	Lockout Procedure Station With Binder & 25 Forms	\$78.82
99289	Lockout Procedure Station With Binder Only	\$73.55
LOSB1	Lockout Procedure Binder Only	\$18.03
LOSF5	Lockout Procedure Forms (25/pkg)	\$9.27



Lockout Clip Board

- Heavy duty, red clipboard allows lockout information and hardware to be conveniently carried directly to the lockout location
- Clipboard can also be hung in place using attached strap
- Lockout safety tips silk-screened onto the back
- Procedure forms (LOSF5), locks and hasps sold separately

Catalog #	Description	Price
LOCB	Lockout Clip Board	\$20.97

OTHER WAYS OF PROVIDING ACCESS TO PROCEDURES

- Print procedures to adhesive or magnetic labels and adhere to directly to machine.
- Attach procedures to work orders manually or by linking the digital procedure file to work orders generated in a computer maintenance management system
- Provide access to procedures online, allowing workers to view and print procedures from their own computer

Brady's Lockout PRO software allows you to implement any of the methods above.

See page 229 for further information on Lockout PRO™ Software.



Fluorescent Protective Envelopes

- Clear envelopes with fluorescent edging, great for color-coding lockout procedures and other shop information
- Durable 8 gauge vinyl construction withstands harsh environments
- Ideal for indoor or outdoor use

Catalog #				
Green	Orange	Yellow	Size	Price
56941	56942	56944	6" x 9"	\$95.03
56945	56946	56948	9" x 12"	\$116.94


25 identical envelopes/pkg



Adhesive & Magnetic Backed Envelopes

- Made of non-glare clear vinyl material
- 8 1/2" x 11"

Catalog #	Description	Price
50961	Adhesive Backed Envelopes (10/pkg)	\$66.92
50962	Magnetic Backed Envelopes (10/pkg)	\$72.27



Lockout Pro™ Graphical Procedure Writing Software

Create Machine-specific procedures in minutes

- Start immediately with easy-to-use templates and built-in defaults
- Access a database of standard graphics, terms, and information
- Insert images to create clear, machine-specific procedures that identify the location of control points
- Print to a standard inkjet or laser printer, or to Brady's GlobalMark® 2 Industrial Label Maker or HandiMark® Portable Label Maker
- Provide viewing and printing access to users in multiple locations with the FREE viewer and HTML viewer applications
- Export to CMMS or ERP

Create, maintain, train, update – with one program

- Use Lockout PRO software's built-in sample energy control policy to develop your own comprehensive energy control program
- Create machine-specific lockout procedures for different locations; ensure that location-specific safety needs are addressed
- Manage and update your procedures with automatic time- and date-stamping
- Train your employees with online tutorials and built-in video training clips in Enterprise versions
- Access current OSHA lockout/tagout standard with a few clicks
- Call to learn about a separate optional annual audit service for your Lockout Pro procedures

Cat. No.	Description	Price
LOPDESK1001	Lockout Pro Desktop Software	\$795.00
LOPCORP2001	Lockout Pro Enterprise Corporate w/ web viewer	\$11,995.00
LOPBASIC3001	Lockout Pro Basic (Only 3 Administrators)	\$5,095.00
LOPADDUSER1	Additional Administrator (adds 1 admin)	\$695.00
99004	GlobalMark2 Multicolor printer + LockoutPro	\$4,150.00
99009	GlobalMark2 ColorCut printer + LockoutPro	\$1,150.00

For more information on the GlobalMark2 printer, view page 143.

NEW!

Create Custom Graphical Lockout/Tagout Procedures Online

Create Graphical Lockout/Tagout Procedures for your facility in minutes. Procedures comply with OSHA's lockout standards for controlling hazardous energy sources.

- Upload your own digital photos
- Download and print from your own printer
- Save for up to 30 days

Try the Custom Design Tool at www.BradyID.com!

Easy as 1, 2, 3!

- 1) Select your category
- 2) Customize your product
- 3) Add to your shopping cart



Create custom procedure in minutes!

Download and print immediately after purchase!

Visual Lockout Procedure Service

www.BradyID.com

Visual Lockout Procedure Service

OSHA's REQUIREMENT: [OSHA CFR 1910.147 The Control of Hazardous Energy].

1910.147(c)(4) synopsis: Machine-specific lockout / tagout procedures are required for equipment having more than one energy source, as well as for much equipment having a single energy source.

GRAPHICAL PROCEDURE SOLUTION:

Complete compliance with OSHA featuring worker-friendly, visually-instructive procedures that reduce the time to safely lock out equipment.



Brady project engineers will come to your facility and:

- **Perform a Zero Energy State Assessment**
Our engineers identify all potential hazardous energy sources and ensure that all energy isolation means are documented in the procedures.
- **Develop Visual Lockout Procedures**
We create effective, safe and easy-to-understand procedures for each piece of equipment, using state-of-the-art electronic tools and digital technology.
- **Install Lockout Procedures**
Durable, laminated visual machine-specific procedures are positioned at optimal locations on the equipment to ensure maximum usability.
- **Create and Install Energy Source Tags**
Heavyweight thermoplastic, color-coded energy source tags are installed at each energy isolation point to visually direct authorized employees to the correct energy source locations.
- **Provide for Easy Maintenance of the Lockout Program**
All electronic files, templates of the procedures, a binder containing additional copies of the procedures, and a training session on maintaining the new lockout program are delivered at the completion of the project.

“It would have taken our internal team months to develop procedures of this quality; but the Brady Program took four days.”

*Pamela Bilger, EHS
Manager Lehigh Valley
Dairy Farms*



Visual Lockout Procedure Service

www.BradyID.com



Visually instructive procedures prevent injuries, save time, and increase productivity.

“The procedures are so simple for our employees to understand which aids in their effectiveness; having the pictures of our equipment on each procedure makes them personalized and easy to follow ... this service is a great asset to anyone’s lockout/tagout program.”

Stacey Zimmerman, Elizabethtown College

! **Get Started Now**

Contact your local Brady sales representative or distributor to set up a Visual Lockout Procedure Assessment for your facility, or call Brady Professional Safety Services at 1-800-496-4040 for a free consultation today.



Facility Safety Signage Assessment Service

www.BradyID.com

Professional Safety Services

Facility Safety Signage Assessment Service

A cost-effective solution to ensure the accuracy and completeness of your facility's safety signage and pipe marking needs.

Professional Inspection

A Brady project manager will inspect your facility, assess your current safety identification program and prepare a comprehensive report providing corrective actions and a complete list of required and recommended identification products.

Fast, Easy & Cost-Effective

Brady will manage every aspect of your safety signage assessment project, saving weeks of industry standard research, internal data collection and extensive project management.

Deliverables: Safety Identification Compliance & Improved Productivity

- Comprehensive report with photographic references providing a full assessment.
- Prioritized corrective action steps with a complete list of signs and markers to improve your facility marking.
- Allows you to meet OSHA, NFPA and other safety ID marking regulations.
- Improves communication by putting critical information at the point of need.
- Eliminates unsafe conditions and reduces both wasted time and operating errors.



Areas of Assessment:

- General safety signage
- Facility pipe marking to meet ANSI standards
- Personal Protective Equipment (PPE) notices
- Electrical panel safety marking
- Exit marking and emergency egress requirements
- Confined space warnings
- Portable fire protection equipment identification
- Safety shower and eyewash identification
- Tank and vessel signage and placards



Get Started Now

Let Brady's Facility Safety Signage Assessment Service identify safety & productivity gains you can't afford to ignore. Contract your local Brady distributor or call Brady Professional Safety Services at 1-800-496-4040 to get started!



Visual Confined Space Procedure Service

OSHA's REQUIREMENT: [OSHA CFR 1910.146 Permit-Required Confined Spaces].

Synopsis: Employers must evaluate the workplace to identify permit-required confined spaces. Procedures must then be developed and implemented to cover acceptable entry conditions for the designated spaces (isolating, purging, ventilating, etc.), use of barriers, providing a full range of equipment (testing, ventilating, PPE, etc.), designating and training active role participants, and more.

GRAPHICAL CONFINED SPACE PROCEDURES SOLUTION:

Provides effective compliance with OSHA's CFR for Permit Required Confined Spaces. Brady's G-CSP solution is presented in a worker-friendly, visually-instructive format, to ensure that hazardous and potentially hazardous confined spaces are always entered properly and safely.

Brady's service professionals will first assess the confined- and potentially confined spaces in your facilities; then develop the visual procedures to provide for safe entry. These documented procedures include:

- Identification of hazards and potential hazards.
- Visual images locating the hazards which may be present.
- A listing of all required equipment and safety devices necessary to enter a confined space.
- Documentation of methods to protect employees from confined space hazards.
- Verifications to ensure that authorized entrants are safe to enter and work in confined spaces.
- Specific procedures are produced for each of your identified confined spaces; providing both full compliance with OSHA and best safety practices.



A perfect complement to Visual Lockout Procedures in your facility; and Confined Space Procedures are additive to them, so the cost per completed procedure is less.



Get Started Now

Quotes can be generated within 48 hours. Call Brady Professional Safety Services at 1-800-496-4040 for further information and consultation today.

Sign Legend Index

www.BradyID.com

Sign Legend	Sign Header	Pg.
\$100 Fine		40
\$250 Fine		40
\$350 Fine		40
480 Volts (w/picto)	Danger	26
A.E.D. (w/picto)		38
Acid	Danger	28
Admittance Limited To Authorized Personnel	Danger	24
All Visitors Must Get Pass At Office	Restricted Area	46
All Visitors Must Register At Office	Notice	25
All Visitors Must Report To Security	Security Notice	46
All Visitors Report To Site Office	Notice	47
Alto Voltaje	Peligro	27
Any Time	No Parking	49
Area In Front Of This Electrical Panel Must Be Kept Clear For 36 In Osha-Nec Regulations		31
Area In Front Of This Electrical Panel Must Be Kept Clear For 36 Inches Osha-Nec Regulations	Caution	31
Area In Front Of This Electrical Panel Must Be Kept Clear For 36 Inches Osha-Nec Regulations	Danger	31
Arrow Picto		33, 36, 49
Asbestos Cancer And Lung Disease Hazard Authorized Personnel Only	Danger	47
Asbestos Cancer And Lung Disease Hazard Authorized Personnel Only Respirators And Protective Clothing Are Required In This Area	Danger	28
Asbestos Cancer And Lung Disease Hazard Do Not Disturb Without Proper Training And Equipment	Caution	29
Asbestos Waste Disposal Site Do Not Create Dust Breathing Asbestos Is Hazardous To Your Health	Caution	29
Attach Grounding Cables	Caution	31
Attention All Visitors And Sales People Please Report To Office		49
Authorized Employees Only	Restricted Area	24
Authorized Personnel Only		24
Authorized Personnel Only	Danger	24
Authorized Personnel Only	Notice	25
Authorized Personnel Only (w/picto)	Notice	25
Authorized Personnel Only (w/picto)	Restricted Area	46
Authorized Personnel Only (w/picto)	Warning	26
Authorized Personnel Only/Solo Personal Autorizado	Notice/Aviso	27
Automatic Start Equipment	Danger	41
Avoid Contamination Wash Your Hands (w/picto)	Notice	25
Bad Planning On Your Part Does Not Necessarily Constitute An Automatic Emergency On My Part		40
Battery Charging Station No Smoking Or Open Flames	Caution	49
Be Alert Don'T Get Hurt		45
Benzene Cancer Hazard	Danger	28
Biohazard (w/picto)		28
Blank		26
Blank	Caution	26
Blank	Danger	26
Blank	Evacuation Map	32
Blank	Notice	26
Blank	Warning	26
Buckle Up And Drive Safely		49
Bump		48
Buried Cable	Caution	31
Buried Cable	Danger	31
Cable Buried Here	Danger	31
Cameras Not Allowed (w/picto)		46
Carbon Monoxide May Be Present	Caution	29
Caustic	Danger	28
Caution Biohazard (w/picto)		28
Caution Radiation Area (w/picto)		45
Caution Radioactive Materials (w/picto)		45
Caution Speed Bump		48
Caution X-Rays This Equipment Produces X-Rays When Energized (w/picto)		45
Chemical Goggles Required In This Area	Caution	44
Chemical Storage	Danger	28
Chlorine	Danger	28
Chlorine Area	Caution	29
Chlorine Gas	Danger	28
Clearance Ft In	Caution	41
Closed Area Authorized Personnel Only		24
Combustible Liquids	Danger	28
Compact Cars Only	Notice	49

Sign Legend	Sign Header	Pg.
Complaint Department (W/Right Arrow) 100 Miles	Notice	40
Confined Space Authorized Personnel Only (w/picto)	Danger	25
Confined Space Enter By Permit Only	Danger	30
Confined Space Enter By Permit Only (w/picto)	Danger	26
Confined Space Enter By Permit Only/Espacio Cerrado Entrada Solo Con Permiso	Danger/Peligro	27
Confined Space Hazardous Atmosphere Check Oxygen Level Before And During Entry	Danger	24
Confined Space Hazardous Atmosphere Entry By Permit Only	Danger	24
Confined Space No Entry Permit Required Call	Caution	25
Confined Space Sign	Caution	30
Construction Area	Danger	24
Construction Area Keep Out	Danger	24
Construction Site Keep Out	Danger	47
Construction Site No Trespassing	Danger	47
Construction Site Unauthorized Persons Keep Out	Danger	47
Construction Zone Unauthorized Personnel Keep Out	Danger	49
Contains Asbestos Fibers Avoid Creating Dust-Cancer And Lung Disease Hazard	Danger	28
Contains Asbestos Fibers Avoid Creating Dust-Cancer And Lung Disease Hazard/Contiene Fibras De Asbesto Evitar La Formacion De Polvo - Peligro De Enfermedad De Los Pulmones Y Cancer	Danger/Peligro	27
Corrosive	Danger	28
Corrosive Liquids Wear Protective Equipment	Danger	28
Corrosive Materials Wear Required Protection	Caution	29
Crosswalk (w/picto)		48
Customer Parking		49
Danger High Voltage		31
Danger Laser Light (w/picto)		45
Danger No Trespassing Positively No Admittance		24
Danger: Laser Light		45
Demolition Work In Progress	Danger	47
Designated Smoking Area		43
Diesel	Danger	28
Diesel Fuel	Danger	28
Diesel Only		29
Do Not Block Door	Notice	30
Do Not Dump Chemicals Down This Drain	Notice	29
Do Not Enter		24, 48, 50
Do Not Enter	Caution	25
Do Not Enter	Danger	24
Do Not Enter Authorized Personnel Only	Danger	24
Do Not Enter Authorized Personnel Only (w/picto)	Restricted Area	46
Do Not Enter Authorized Personnel Only/No Entre Solo Personal Autorizado	Danger/Peligro	27
Do Not Enter When Lights Are Flashing	Danger	24
Do Not Enter Without A Confined Space Permit	Caution	25
Do Not Operate This Machine Without Guards In Place	Caution	41
Do Not Operate Without Guards	Caution	41
Do Not Operate Without Guards In Place (w/picto)	Danger	25
Do Not Watch The Arc	Danger	41
Double Hearing Protection Required In This Area	Caution	44
Drivers Chock Both Wheels		49
Ear Hazard Area Ear Protection Required At All Times	Caution	44
Ear Protection Area (w/picto)		39
Ear Protection Must Be Worn In This Area	Caution	44
Ear Protection Required (w/picto)	Caution	44
Ear Protection Required When This Equipment Is Operating	Caution	44
Electrical (w/picto)		31
Electrical Closet No Storage Permitted	Notice	31
Electrical Equipment Authorized Personnel Only		31
Electrical Equipment Authorized Personnel Only	Danger	24, 31
Electrical Equipment Authorized Personnel Only (w/picto)	Danger	25, 31
Electrical Hazard Authorized Personnel Only	Danger	24
Elevator (Braille W/Picto)		26
Emergency Evacuation In Case Of Fire Use Stairway For Exit Do Not Use Elevator		32
Emergency Evacuation Route (w/Left Arrow)		34
Emergency Evacuation Route (w/Right Arrow)		34
Emergency Exit		34
Emergency Exit (w/picto)		34
Emergency Exit Only		33
Emergency Exit Only: Alarm Will Sound		33

Sign Legend Index

www.BradyID.com

Sign Legend	Sign Header	Pg.
Emergency First Aid Guide (Etc.)		52
Emergency Fuel Shutoff		29
Emergency Phone Numbers Fire Dept Police Dept Ambulance Medical		34
Emergency Shower And Eye Wash/Ducha De Emergencia Y Para		
Lavar Los Ojos (w/picto)		27
Emergency Shut Off		36
Emergency Stop Button		41
Employees Only	Notice	25
Employees Only	Parking	49
Empty Cylinders		29
Enter Only		48
Evacuation Assembly Area		36
Evacuation Map		32
Evacuation Map In Case Of Fire Do Not Use Elevators Use Stairways		32
Exit		32-37, 48
Exit (Braille)		26
Exit (Double Arrow)		34
Exit (w/picto)		33-39
Exit (W/Running Man - Arrow Left Down)		35
Exit (W/Running Man - Arrow Left Up)		35
Exit (W/Running Man - Arrow Left)		35
Exit (W/Running Man - Arrow Right Down)		35
Exit (W/Running Man - Arrow Right Up)		35
Exit (W/Running Man - Arrow Right)		35
Exit Only		24
Exit Only		48
Exit Through Lobby		35
Exit/Salida		34
Explosives	Danger	29
Eye And Ear Protection Must Be Worn Beyond This Point	Caution	45
Eye And Ear Protection Required While Operating This Equipment	Danger	41
Eye And Glove Protection Must Be Worn When Handling Chemicals	Caution	29
Eye Protection And Hard Hats Must Be Worn In This Area	Caution	45
Eye Protection Area (w/picto)		39
Eye Protection Required	Caution	30
Eye Protection Required (w/picto)	Caution	44
Eye Protection Required In This Area	Safety First	44
Eye Protection Required In This Area (w/picto)	Caution	25
Eye Protection Required In This Area (w/picto)	Danger	25
Eye Protection Required/Se Requiere Proteccion Para La Vista	Caution/Precaucion	27
Eye Wash		38
Eye Wash (w/picto)		38
Eye Wash Fountain	Safety First	38
Eye Wash Station		38
Eye Wash Station (w/picto)		38
Eye Wash Station Keep Area Clear (w/picto)	Emergency	25, 38
Face Shield Area	Caution	44
Falling Material	Danger	41
Final Exit		35
Fire Alarm		36
Fire Alarm (w/down arrow)		37
Fire Alarm (w/down arrow and picto)		37
Fire Alarm (w/picto)		34, 36
Fire Door Do Not Block	Caution	30
Fire Door Keep Closed		30
Fire Door Keep Closed	Caution	30
Fire Equipment (w/down arrow)		37
Fire Equipment Keep Clear		36
Fire Extinguisher		36
Fire Extinguisher (w/down arrow)		37
Fire Extinguisher (w/picto)		26, 34
Fire Extinguisher (w/picto)		37, 39
Fire Extinguisher Do Not Block/Extintor De Incendios No Bloquear		34
Fire Extinguisher Here		36
Fire Extinguisher Inside		36
Fire Extinguisher Inside (w/picto)		36
Fire Extinguisher (w/down arrow)		36
Fire Extinguisher (w/down arrow and picto)		37
Fire Extinguisher/Extintor De Incendios (w/picto)		27, 34
Fire Hose		36, 37
Fire Hose (w/picto)		34
Fire Hose w/Down Arrow (w/picto)		37
Fire Lane Keep Clear At All Times	No Parking	36

Sign Legend	Sign Header	Pg.
Fire Lane Keep Clear At All Times	Notice	36
Fire-Police-Medical Emergency Dial 911		34
First Aid (w/picto)		34, 38
First Aid Kit	Safety First	38
First Aid Kit (w/picto)		38
First Aid Station	Safety First	38
First Aid Station (w/picto)	Emergency	25
Flammable Gas	Danger	28
Flammable Keep Fire Away	Danger	29
Flammable Keep Flames And Heat Away	Danger	29
Flammable Liquids	Danger	28
Flammable Material No Smoking	Danger	28
Flammable Material No Smoking Within 20 Feet	Danger	28
Flammable Materials	Danger	28
Flammable No Smoking Or Open Flame Within Feet		43
Floor Load Limit Not To Exceed Lbs Sq Ft	Caution	42
Floor Slippery When Wet (w/picto)	Caution	25
Follow Lockout/Tagout Procedures (w/picto)	Danger	25
Foot Protection Required	Caution	45
Fork Lift Trucks Operating Beyond This Point	Caution	47
Forklift Traffic Keep Clear (w/picto)	Caution	25
Full Cylinders		29
Gas	Danger	28
Gasoline No Smoking (w/picto)	Danger	29
Gloves Required	Caution	45
H2S May Be Present	Danger	28
H2S Poisonous Gas	Danger	28
Hair Net Required Beyond This Point	Notice	45
Handicapped (Braille w/Picto)		26
Handicapped Parking (w/picto)		40
Handicapped Parking Only (w/picto)		40
Handicapped Parking Permit Required (w/picto)		40
Handicapped Parking Towing Enforced (w/picto)		40
Handicapped Parking Van Accessible		40
Handicapped Picto		40
Handicapped Picto w/Left Arrow		40
Handicapped Picto w/Right Arrow		40
Hard Hat Area	Danger	41
Hard Hat Area (w/picto)		39
Hard Hat Area (w/picto)	Danger	45
Hard Hat Protection Required	Danger	45
Hard Hat Required In This Area (w/picto)	Danger	25
Hard Hats Ear And Eye Protection Required Beyond This Point	Danger	45
Hard Hats Must Be Worn On This Construction Project	Notice	45
Hard Hats Required	Caution	30
Hard Hats Required (w/picto)	Caution	45
Hard Hats Required/Casco De Proteccion Requerido	Caution/Precaucion	27
Hazard Area No Unauthorized Personnel Beyond This Point	Danger	24
Hazardous Area	Danger	28
Hazardous Chemicals	Danger	28
Hazardous Material Area Authorized Personnel Only	Danger	28
Hazardous Waste Material Storage Only No Smoking, Open Flames Or Open Lights	Caution	29
Hazardous Waste Storage Area Unauthorized Persons Keep Out	Caution	29
Hazardous Waste Storage Area Unauthorized Persons Keep Out	Danger	24
Hearing Protection Must Be Worn In This Area	Caution	44
Hearing Protection Must Be Worn In This Area	Notice	44
Hearing Protection Required	Caution	30
Hearing Protection Required (w/picto)	Caution	44
Hearing Protection Required Beyond This Point	Caution	47
Hearing Protection Required In This Area (w/picto)	Caution	26
Hearing Protection Required/Proteccion Auditiva Requerida	Caution/Precaucion	27
High Noise Level Use Ear Protection	Caution	44
High Voltage	Danger	24, 31
High Voltage (w/picto)		31
High Voltage (w/picto)	Danger	25, 31
High Voltage Above (w/picto)	Danger	31
High Voltage Keep Away (w/picto)	Danger	31
High Voltage Keep Out	Danger	24, 31
High Voltage Keep Out/Alto Voltaje Mantengase Afuera	Danger/Peligro	27
High Voltage Overhead	Danger	31
High Voltage Turn Power Off Before Servicing (w/picto)	Danger	25
High Voltage Unauthorized Personnel Keep Out	Danger	24

Sign Legend Index

www.BradyID.com

Sign Legend	Sign Header	Pg.
High Voltage Underground Cable	Danger	31
High Voltage Volts	Danger	31
High Voltage Within Keep Out (w/picto)	Danger	31
High Voltage: Do Not Enter This Enclosure	Caution	31
High Voltage/Alto Voltaje	Danger/Peligro	27
Hot	Caution	41
Hot (w/picto)	Danger	25
Hot Surface Do Not Touch (w/picto)	Danger	41
In Case Of Fire Do Not Use Elevators...Etc (w/picto)		33
Keep Aisles Clear (w/picto)		39
Keep All Cylinders Chained (w/picto)	Danger	29
Keep Electric Panel Area Clear	Caution	31
Keep Gates Closed		40
Keep Off	Danger	24
Keep Out	Danger	24
Keep Out Hazard Area	Danger	24
Keep Right		48
Keep This Door Closed	Notice	25
Keep This Place Clean And Orderly		42
Live Wire Overhead (w/picto)	Danger	31
Lock Out For Safety (w/picto)	Caution	41
Lock Out Here (w/picto)		41
Lockout Center (w/picto)		41
Look Out For Lift Trucks	Danger	41
Low Overhead Clearance	Caution	41
Lp Gas Storage No Smoking Or Open Flames Within 50 Ft	Danger	28
Machine Starts Automatically Keep Hands Away	Caution	41
Men (Braille w/picto)		26
Men (w/picto)		46
Men Working		50
Men Working	Danger	41
Men Working Above	Danger	41, 47
Men Working Above (w/up arrow)	Danger	41
Motorcycle Parking Only		49
No Admittance Authorized Persons Only		24
No Admittance Employees Only (w/picto)	Restricted Area	46
No Admittance Except For Assigned Employees And Personnel Of Carriers Who Are Engaged In Authorized Deliveries Or Pick-Up		24
Visitors Secure Pass At The Plant Office		24
No Beverages Or Food Allowed In This Area		42
No Bicycles Skateboards Rollerblades (w/picto)		46
No Cellular Phones (w/picto)		42, 46
No Cellular Phones Allowed (w/picto)	Notice	42
No Dumping Violators Will Be Prosecuted		46
No Eating Or Drinking In This Area	Notice	42
No Entry Unless Authorized (w/picto)	Notice	25
No Exit		24, 34
No Exit	Notice	33
No Exit/No Hay Salida		34
No Firearms Allowed On Premises (w/picto)	Notice	25
No Food Or Drink Beyond This Point	Notice	42
No Guns Allowed Beyond This Point (w/picto)		46
No Parking		49
No Parking	Notice	49
No Parking Any Time		49
No Parking Fire Lane		49
No Parking Loading Zone		49
No Smoking		34, 43
No Smoking	Danger	26, 43
No Smoking (w/picto)		43
No Smoking At Anytime		43
No Smoking Beyond This Door		43
No Smoking Beyond This Point		43
No Smoking In This Area		43
No Smoking In This Area (w/picto)		26
No Smoking In This Building It's The Law		43
No Smoking In This Facility		43
No Smoking Matches Or Open Lights	Danger	43
No Smoking No Open Flames	Oxygen	29
No Smoking No Open Flames No Sparks	Danger	43
No Smoking On Premises		43
No Smoking Or Open Lights Within Feet	Danger	43
No Smoking This Area		43

Sign Legend	Sign Header	Pg.
No Smoking Violators Are Subject To Fine.		43
New Jersey Smoke-Free Air Act N.J.S.A 26:3D-55		43
No Smoking Within Feet		43
No Smoking, Eating Or Drinking In This Area (w/picto)	Warning	26
No Smoking/No Fumar (w/picto)		27
No Smoking/No Fumar (w/picto)	Danger/Peligro	27
No Thru Traffic		48
No Trespassing		24
No Trespassing	Danger	24
No Trespassing	Notice	25
No Trespassing Violators Will Be Prosecuted		48
No Trespassing/No Traspase	Notice/Aviso	27
No Trucks		49
No Trucks Picto		49
No U-Turn		49
No Unauthorized Personnel Beyond This Point	Restricted Area	24
No Vehicles Beyond This Point		48
No Whining (w/picto)		40
Nobody Notices What I Do Until I Don'T Do It		40
Non-Potable Water	Notice	29
Non-Potable Water Do Not Drink	Caution	29
Non-Potable Water Do Not Use For Drinking, Washing Or Cooking Purposes (w/picto)	Danger	29
Non-Potable Water Not For Drinking Or Cooking (w/picto)	Notice	29
Non-Potable Water Not For Drinking Or Cooking Use	Notice	29
Non-Potable Water Not For Drinking Or Cooking Use/ Agua No Potable No Apta Para Beber Ni Cocinar	Notice/Aviso	27
Not An Exit		33, 34
Not An Exit/No Es Salida		34
Notice No Trespassing Loitering Soliciting On This Property		46
One Way (w/picto)		38, 48
One Way Do Not Enter		48
Open Door Slowly	Caution	30
Open Hole	Danger	44
Open Pit	Danger	44
Overhead Work	Caution	41
Pacemaker Wearer Do Not Enter This Room Microwave Ovens In Use	Danger	45
Park At Your Own Risk		49
Parking (w/picto)		40
Parking Facilities Under Camera Surveillance And Security Patrols	Notice	49
Ped Xing		48
Pedestrian Traffic Only W/Picto		39
Pedestrians Picto		48
Permit-Required Confined Space Do Not Enter	Danger	30
Personal Protective Equipment Required Beyond This Point	Caution	45
Pinch Point Keep Hands Clear (w/picto)	Caution	25
Pinch Point Watch Your Hands (w/picto)	Danger	41
Pinch Points Watch Your Hands (w/picto)	Danger	25
Positively No Smoking Allowed On These Premises	Notice	43
Practice Good Housekeeping A Place For Everything And Everything In Place		42
Private Property No Hunting No Trespassing		24
Private Property No Parking... Etc		48
Private Property No Trespassing		24, 48
Private Property No Trespassing Violators Will Be Prosecuted		46
Private Property Trespassers Will Be Prosecuted To The Full Extent Of The Law		24
Propane Gas	Danger	28
Push		35
Receiving		49
Recyclable Waste Only (w/picto)		46
Report All Accidents No Matter How Small To Your Foreman	Safety First	38
Reserved Parking		49
Reserved Parking (w/double arrow and picto)		40
Restricted Area Authorized Personnel Only	Notice	25
Restricted Area Keep Out	Notice	25
Restrooms (Braille w/picto)		26
Safety Glasses Required (w/picto)		39
Safety Glasses Required Beyond This Point	Caution	44
Safety Glasses Required Beyond This Point	Notice	30
Safety Glasses Required In This Area	Caution	44
Safety Glasses Required In This Area	Danger	44
Safety Glasses Required In This Area	Notice	44

Sign Legend Index

www.BradyID.com

Sign Legend	Sign Header	Pg.
Safety Glasses Safety Shoes And Hard Hats Required Beyond This Point	Safety First	45
Safety Goggles Required (w/picto)		39
Safety Shoes Required (w/picto)	Caution	45
Safety Shower		38
Safety Shower And Eyewash Station	Safety First	38
Security Badges Must Be Worn At All Times	Security Notice	46
Severe Weather Shelter Area (w/picto)		34
Severe Weather Shelter Area (w/Tornado Picto)		34
Shipping And Receiving		48, 49
Slippery Floor	Caution	44
Slippery When Wet	Caution	44
Slow		48
Slow Children (w/picto)		48
Smoking In Designated Areas Only		43
Smoking Permitted In This Area		43
Solo Personal Autorizado	Aviso	27
Speed Limit 10 Mph		48
Speed Limit 15 Mph		48
Speed Limit 20 Mph		48
Speed Limit 25 Mph		48
Speed Limit 5 Mph		48
Spill Station		41
Spill-Kit Station		29
Sprinkler Valve		34
Stairs		34
Stairway (braille w/picto)		26
Starts Automatically	Danger	41
Stay Clear	Danger	41
Stay Clear Of Moving Conveyors	Danger	41
Stay Clear Of Swing Radius	Danger	41
Stop		39, 48, 50
Stop / Slow		50
Stop Ahead		48
Stop Eye Protection Required Beyond This Point		45
Stop Sound Horn Proceed Slowly		49
Stop Tank Car Connected		49
Thank You For Not Smoking		43
This Area Is Under 24 Hour Tv Surveililance Trespassers Will Be Prosecuted (w/picto)		46
This Company Has Worked [#] Days Without A Lost Time Accident The Previous Record Was [#] Days Do Your Part Help Make A New Record!		46
This Department Has Worked [#] Days Without A Disabling Injury The Previous Record Was [#] Days Do Your Part Help Make A New Record!		46
This Department Has Worked [#] Days Without A Lost Time Accident The Previous Record Was [#] Days Do Your Part Help Make A New Record!		46
This Door To Remain Unlocked During Business Hours		30
This Equipment Is Supplied With Two Electrical Services	Danger	41
This Equipment Starts Automatically	Danger	41
This Is A Smoke Free Work Place (w/picto)		43
This Machine Must Be Locked Out Prior To Servicing	Caution	41
This Plant Has Worked [#] Days Without A Disabling Injury The Previous Record Was [#] Days Do Your Part Help Make A New Record!		46
This Plant Has Worked [#] Days Without A Lost Time Accident The Previous Record Was [#] Days Do Your Part Help Make A New Record!		46
This Property Is Protected By Electronic Surveillance (w/picto)	Security Notice	46
This Property Protected By Electronic Surveillance	Notice	25, 46
This Space Must Be Kept Clear At All Times	Caution	42
This Way Out (w/picto)		34
Tornado Shelter (w/picto)		30, 34
Tripping Hazard	Caution	44
Truck Drivers Must Chock Wheels And Set Brakes Before Loading Or Unloading		49
Truck Drivers Shut Off Motor Set Brakes Set Wheel Chocks	Notice	49
Turn Off Lights Conserve Energy		46
Two Way Feed	Danger	41
Unauthorized Personnel Keep Out	Danger	24
Unauthorized Persons Keep Out	Restricted Area	24

Sign Legend	Sign Header	Pg.
Underground Cable	Danger	31
Use Handrail	Caution	44
Use Of Cellular Phones Not Allowed		46
Used Oil		29
Van Accessible		40
Vehicles Must Come To A Complete Stop Before Proceeding (w/picto)		40
Video Surveillance In Use On These Premises (w/picto)	Security Notice	46
Visitor Parking		49
Visitors Parking Only		49
Volts	Danger	31
Warning Forklift Traffic W/Picto		39
Warning This Machine Is Automatically Controlled And May Start At Any Time		41
Wash Hands Before Returning To Work	Notice	45
Wash Your Hands Before Leaving This Room	Notice	45
Wash Your Hands Before Leaving This Room/ Lavesse Las Manos Antes De Salir De Este Cuarto	Notice/Aviso	27
Watch For Lift Trucks (w/picto)	Caution	41
Watch For Lift Trucks/Mire La Salida De Los Camiones	Caution/Precaucion	27
Watch Out For Falling Ice	Caution	42
Watch Out For Fork Lift Trucks (w/picto)	Caution	41
Watch Out For Fork Truck Operating In Area	Caution	41
Watch Out For Forklift Trucks (w/picto)		39
Watch Out For Forklift Trucks/Mire La Salida De Los Camiones (w/picto)	Caution/Precaucion	27
Watch Out For Trucks	Caution	29
Watch Your Step	Caution	44
Watch Your Step (w/picto)		39
Watch Your Step (w/picto)	Caution	39, 44
Wear Goggles	Safety First	44
Wear Safety Shoes In This Area	Caution	45
Welding Fumes May Be Present	Caution	29
Wheelchair Ramp (w/picto)		40
Wheels Must Be Chocked And Engine Turned Off During Loading	Notice	49
Wheels Must Be Chocked Before Loading Or Unloading (w/picto)	Safety First	49
Women (Braille W/Picto)		26
Women (w/picto)		46
Wrong Way		48
Yield		48, 50

Part Number Index

www.BradyID.com

Part Number Index

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
2001	\$148.21	58	13537	\$266.82	151	13616	\$266.82	150	22112	\$13.90	24
2002	\$148.21	58	13538	\$148.21	150	13617	\$266.82	150	22114	\$13.90	24
2005	\$51.73	58	13539	\$148.21	150	13618	\$266.82	150	22141	\$9.81	25
2007	\$83.78	58	13540	\$148.21	150	13620	\$14.48	158	22142	\$13.90	25
2010	\$72.96	58	13541	\$148.21	150	13621	\$14.48	158	22144	\$13.90	25
2011	\$33.82	103	13542	\$148.21	150	13622	\$14.48	158	22163	\$9.81	25
2012	\$118.65	58	13543	\$148.21	150	13623	\$31.92	158	22164	\$13.90	25
2014	\$31.85	58	13544	\$148.21	150	13624	\$31.92	158	22178	\$13.90	24
2019	\$33.82	103	13545	\$148.21	150	13625	\$31.92	158	22186	\$13.90	24
2022	\$36.13	59	13546	\$148.21	150	13626	\$46.47	158	22190	\$13.90	24
2023	\$20.79	59	13547	\$148.21	150	13627	\$46.47	158	22208	\$13.90	24
2024	\$29.08	59	13548	\$148.21	150	13628	\$46.47	158	22214	\$13.90	24
2025	\$30.45	59	13549	\$177.86	150	13629	\$40.10	158	22218	\$13.90	24
2026	\$20.79	59	13550	\$177.86	150	13630	\$40.10	158	22227	\$9.81	24
2027	\$29.08	59	13551	\$222.32	150	13631	\$40.10	158	22233	\$13.90	24
2028	\$30.45	59	13552	\$222.32	150	13632	\$53.95	158	22249	\$13.90	24
2032	\$55.22	59	13553	\$222.32	150	13633	\$53.95	158	22273	\$13.90	29
2112	\$33.33	226	13554	\$222.32	150	13634	\$53.95	158	22295	\$13.90	28
3001	\$296.37	193	13555	\$222.32	150	13635	\$78.90	158	22312	\$13.90	28
3002	\$299.31	193	13556	\$222.32	150	13636	\$78.90	158	22324	\$13.90	28
3012	\$134.70	193	13557	\$222.32	150	13637	\$78.90	158	22399	\$9.81	30
3013	\$134.70	193	13558	\$222.32	150	13638	\$43.58	158	22400	\$13.90	30
12900	\$71.01	156	13559	\$222.32	150	13639	\$58.11	158	22406	\$13.90	30
12901	\$71.01	156	13560	\$222.32	150	13640	\$87.18	158	22407	\$9.81	30
12902	\$71.01	156	13561	\$222.32	150	13644	\$12.70	149	22408	\$13.90	30
12903	\$71.01	156	13562	\$266.82	150	13651	\$207.51	150	22424	\$9.81	30
12904	\$71.01	156	13563	\$266.82	150	13652	\$207.51	150	22425	\$13.90	30
12905	\$71.01	156	13564	\$163.01	150	13653	\$207.51	150	22430	\$13.90	24
12906	\$71.01	156	13565	\$163.01	150	13654	\$207.51	150	22432	\$13.90	24
12907	\$71.01	156	13566	\$163.01	150	13655	\$207.51	150	22455	\$9.81	33
12908	\$71.01	156	13567	\$163.01	150	13656	\$207.51	150	22456	\$13.90	33
12909	\$71.01	156	13568	\$200.09	150	13700	\$334.94	149	22457	\$9.81	33
12910	\$71.01	156	13569	\$200.09	150	13704	\$207.51	151	22458	\$13.90	33
12911	\$71.01	156	13570	\$200.09	150	13705	\$207.51	151	22467	\$13.90	38
12912	\$71.01	156	13571	\$200.09	150	13706	\$229.74	151	22480	\$9.81	33
12913	\$71.01	156	13572	\$222.32	150	13707	\$229.74	151	22481	\$9.81	33
12914	\$71.01	156	13573	\$222.32	150	1530-*	\$52.23	66	22482	\$13.90	33
12921	\$71.01	156	13574	\$222.32	150	1534-*	\$89.20	66	22483	\$9.81	33
12922	\$71.01	156	13575	\$222.32	150	15424	\$46.02	154	22484	\$13.90	33
12923	\$71.01	156	13576	\$296.48	150	1550-*	\$132.79	66	22488	\$9.81	33
12924	\$71.01	156	13577	\$296.48	150	17927	\$50.45	72	22489	\$9.81	33
12925	\$71.01	156	13578	\$296.48	150	19811	\$61.93	51	22490	\$13.90	33
12926	\$71.01	156	13579	\$296.48	150	19931	\$9.81	31	22492	\$13.90	33
13027	\$71.01	156	13580	\$198.47	150	19935	\$11.53	31	22494	\$9.81	24
13402	\$366.46	150	13582	\$198.47	151	19938	\$19.74	31	22498	\$9.81	33
13403	\$274.82	150	13583	\$192.69	151	2010DB	\$138.42	58	22499	\$9.81	24
13404	\$198.47	150	13584	\$192.69	151	2010DBSP	\$138.42	58	22499	\$9.81	24
13500	\$4,995.00	148	13585	\$274.82	150	2010NB	\$57.33	58	22500	\$13.90	33
13507	\$40.13	149	13587	\$274.82	151	2010SP	\$71.55	58	22501	\$9.81	33
13510	\$200.09	151	13588	\$266.82	151	2011L	\$47.37	103	22502	\$13.90	33
13511	\$177.86	151	13589	\$266.82	151	2014W	\$31.85	58	22510	\$13.90	30
13512	\$200.09	151	13590	\$366.46	150	2019L	\$47.37	103	22512	\$13.90	30
13513	\$177.86	151	13592	\$366.46	151	20585	\$147.65	159	22515	\$9.81	30
13514	\$200.09	151	13593	\$355.79	151	20589	\$133.95	159	22516	\$13.90	30
13515	\$200.09	151	13594	\$355.79	151	20602	\$81.84	159	22530	\$13.90	30
13516	\$200.09	151	13595	\$177.86	151	20700L	\$624.37	84	22538	\$13.90	25
13517	\$200.09	151	13596	\$177.86	151	20711L	\$724.89	84	22560	\$9.81	30
13518	\$200.09	151	13597	\$177.86	151	2112SP	\$33.33	226	22587	\$13.90	44
13519	\$200.09	151	13598	\$177.86	151	2112SP-TEN	\$12.88	226	22593	\$13.90	44
13520	\$229.74	151	13599	\$177.86	151	2112-TEN	\$12.88	226	22594	\$9.81	44
13521	\$207.51	151	13600	\$177.86	151	21700	\$9.81	25	22595	\$13.90	44
13522	\$229.74	151	13601	\$177.86	150	21709	\$9.81	25	22615	\$13.90	44
13523	\$207.51	151	13602	\$177.86	150	21713	\$9.81	25	22626	\$9.81	44
13524	\$229.74	151	13603	\$177.86	150	21795	\$9.81	25	22627	\$13.90	30
13525	\$207.51	151	13604	\$177.86	150	21801	\$9.81	25	22629	\$13.90	44
13526	\$229.74	151	13605	\$177.86	150	21806	\$9.81	25	22642	\$9.81	38
13527	\$207.51	151	13606	\$177.86	150	21807	\$9.81	25	22645	\$13.90	38
13528	\$229.74	151	13607	\$177.86	150	21866	\$9.81	25	22650	\$9.81	38
13529	\$207.51	151	13608	\$177.86	150	22059	\$9.81	25	22655	\$13.90	38
13530	\$296.48	151	13609	\$177.86	150	22060	\$13.90	25	22662	\$13.90	38
13531	\$266.82	151	13610	\$266.82	150	22062	\$13.90	25	22665	\$9.81	38
13532	\$296.48	151	13611	\$266.82	150	22092	\$13.90	24	22671	\$9.81	38
13533	\$266.82	151	13612	\$266.82	150	22094	\$13.90	24	22686	\$9.81	38
13534	\$296.48	151	13613	\$266.82	150	22104	\$13.90	31	22697	\$9.81	29
13535	\$266.82	151	13614	\$266.82	150	22105	\$9.81	24	22722	\$13.90	28
13536	\$296.48	151	13615	\$266.82	150	22106	\$13.90	24	22773	\$13.90	42

Part Number Index

www.BradyID.com

Part Number Index

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
40813	\$19.74	24	4150-*	\$4.63	79	42507	\$19.74	41	43246	\$19.74	28
40815	\$19.74	24	4151-*	\$4.63	79	42508	\$11.87	41	43258	\$19.74	36
4081-*	\$4.63	79	4152-*	\$4.63	79	42509	\$19.74	41	43285	\$19.74	36
4082-*	\$4.63	79	4153-*	\$4.63	79	42525	\$19.74	41	43290	\$11.87	36
4083-*	\$4.63	79	4155-*	\$4.63	79	42531	\$19.74	41	43294	\$19.74	36
40846	\$11.87	29	4162-*	\$4.63	79	42535	\$19.74	41	43295	\$11.87	36
4085-*	\$4.63	79	4172-*	\$4.63	79	42556	\$11.87	41	43322	\$11.87	29
4086-*	\$4.63	79	4173-*	\$4.63	79	42562	\$11.87	41	43323	\$11.87	29
40876	\$19.74	28	4185-*	\$4.63	79	42563	\$19.74	41	43339	\$19.74	33
40882	\$19.74	29	41920	\$2.18	74	42621	\$11.87	41	43369	\$19.74	49
40888	\$19.74	28	41920	\$2.18	74	42646	\$19.74	28	43381	\$19.74	24
40892	\$19.74	28	41921	\$2.36	74	42654	\$19.74	43	43382	\$19.74	49
4089-*	\$4.63	79	41921	\$2.36	74	42658	\$19.74	43	43400	\$19.74	49
40906	\$19.74	28	41922	\$2.18	74	42659	\$11.87	43	43406	\$19.74	49
4091-*	\$4.63	79	41922	\$2.18	74	42660	\$19.74	43	43408	\$19.74	49
4092-*	\$4.63	79	41923	\$2.36	74	42662	\$19.74	43	43413	\$19.74	49
40964	\$19.74	30	41923	\$2.36	74	42670	\$19.74	43	43416	\$19.74	49
40970	\$19.74	30	41924	\$2.18	74	42685	\$11.87	43	43422	\$19.74	49
40972	\$19.74	30	41924	\$2.18	74	42687	\$11.87	43	43429	\$19.74	49
4097-*	\$4.63	79	41925	\$2.36	74	42692	\$11.87	43	43431	\$19.74	49
40988	\$11.87	30	41925	\$2.36	74	42693	\$19.74	43	43437	\$19.74	49
40989	\$19.74	30	41926	\$2.18	74	42695	\$19.74	43	43447	\$19.74	49
4098-*	\$4.63	79	41926	\$2.18	74	42696	\$11.87	43	43448	\$19.74	49
4099-*	\$4.63	79	41927	\$2.36	74	42697	\$19.74	43	43469	\$19.74	44
4100-*	\$4.63	79	41927	\$2.36	74	4270-*	\$4.63	79	43471	\$19.74	44
41020	\$19.74	33	41928	\$2.18	74	42712	\$19.74	43	43472	\$19.74	45
41022	\$19.74	33	41928	\$2.18	74	42714	\$19.74	43	43474	\$19.74	31
4102-*	\$4.63	79	41929	\$2.36	74	42715	\$11.87	29	43476	\$19.74	45
4103-*	\$4.63	79	41929	\$2.36	74	42721	\$11.87	43	43477	\$19.74	31
41044	\$11.87	33	4197-*	\$4.63	79	42725	\$19.74	43	43478	\$19.74	25
41046	\$19.74	33	4199-*	\$4.63	79	42753	\$11.87	31	43479	\$19.74	25
41052	\$11.87	33	42004	\$61.94	124	42778	\$19.74	45	43481	\$19.74	38
41053	\$11.87	33	42006	\$123.83	124	42782	\$19.74	45	43483	\$19.74	41
41054	\$19.74	33	42007	\$44.47	124	42784	\$19.74	45	43487	\$19.74	28
4105-*	\$4.63	79	42008	\$93.44	124	42792	\$19.74	45	43489	\$19.74	43
41062	\$11.87	33	42009	\$13.91	124	42794	\$19.74	45	43490	\$19.74	41
41065	\$11.87	33	42010	\$83.48	124	42822	\$19.74	45	43496	\$19.74	29
41066	\$19.74	33	42011	\$33.44	124	42862	\$19.74	45	43499	\$19.74	29
4106-*	\$4.63	79	42012	\$33.44	124	42865	\$19.74	45	43500	\$19.74	41
41076	\$19.74	30	42013	\$33.44	124	42923	\$19.74	45	43517	\$11.87	30
4107-*	\$4.63	79	42014	\$33.44	124	42933	\$11.87	26	43518	\$19.74	30
41080	\$19.74	30	42015	\$33.44	124	42934	\$19.74	26	43983	\$8.38	29
4108-*	\$4.63	79	42062	\$113.74	125	42937	\$11.87	26	44104	\$2.88	70
41094	\$19.74	30	42063	\$164.16	125	42938	\$19.74	26	44110	\$2.88	70
41102	\$19.74	25	42064	\$113.74	125	42941	\$11.87	26	44115	\$2.88	70
4110-*	\$4.63	79	42065	\$164.16	125	42942	\$19.74	26	44129	\$2.88	70
4111-*	\$4.63	79	42066	\$113.74	125	42950	\$19.74	26	44131	\$2.88	70
4113-*	\$4.63	79	42067	\$164.16	125	42952	\$17.17	26	44159	\$2.88	70
4114-*	\$4.63	79	42068	\$40.26	125	42953	\$9.97	26	44160	\$2.88	70
41156	\$11.87	44	42069	\$51.79	125	42954	\$17.17	26	44204	\$2.88	70
41159	\$19.74	44	42071	\$71.97	125	43006	\$19.74	28	44210	\$2.88	70
41191	\$19.74	30	42072	\$334.41	124	43013	\$11.87	28	44215	\$2.88	70
41193	\$19.74	44	42073	\$210.54	124	43014	\$19.74	28	44229	\$2.88	70
4119-*	\$4.63	79	42100	\$50.36	125	43034	\$19.74	44	44231	\$2.88	70
41219	\$19.74	38	42101	\$70.52	125	43042	\$19.74	44	44259	\$2.88	70
4121-*	\$4.63	79	42102	\$106.53	125	43068	\$19.74	44	44260	\$2.88	70
41229	\$11.87	38	42103	\$50.36	125	43083	\$11.87	31	44304	\$2.88	70
4122-*	\$4.63	79	42104	\$70.52	125	43108	\$19.74	31	44310	\$2.88	70
4123-*	\$4.63	79	42105	\$106.53	125	43109	\$11.87	31	44315	\$2.88	70
4124-*	\$4.63	79	42137	\$57.55	125	43110	\$19.74	31	44329	\$2.88	70
41253	\$19.74	36	42138	\$76.28	125	43116	\$19.74	31	44331	\$2.88	70
41262	\$19.74	29	42139	\$113.74	125	43118	\$19.74	31	44359	\$2.88	70
4127-*	\$4.63	79	42211	\$38.17	70	43124	\$19.74	31	44360	\$2.88	70
41284	\$19.74	29	42248	\$2.79	226	43127	\$11.87	31	44400	\$45.05	74
4128-*	\$4.63	79	4225-*	\$4.63	79	43128	\$19.74	31	44401	\$45.05	74
4129-*	\$4.63	79	4226-*	\$4.63	79	43130	\$19.74	31	44402	\$58.79	74
41314	\$19.74	28	42387	\$19.74	41	43134	\$19.74	31	44403	\$58.79	74
4132-*	\$4.63	79	42433	\$19.74	41	43139	\$11.87	31	45009	\$13.19	26
41337	\$19.74	42	42440	\$11.87	41	43160	\$19.74	44	45018	\$23.93	26
4134-*	\$4.63	79	42441	\$19.74	41	43176	\$19.74	42	45072	\$13.90	26
4136-*	\$4.63	79	42442	\$11.87	41	43178	\$19.74	44	45096	\$13.90	26
4140-*	\$4.63	79	42447	\$19.74	41	43187	\$11.87	44	45117	\$8.38	26
4143-*	\$4.63	79	42455	\$19.74	41	43188	\$19.74	44	45159	\$8.38	26
4146-*	\$4.63	79	4247-*	\$4.63	79	43198	\$19.74	44	45191	\$43.02	211
4147-*	\$4.63	79	42489	\$19.74	41	43238	\$19.74	28	45192	\$43.02	211
4148-*	\$4.63	79	42501	\$19.74	41	43244	\$19.74	28	45331	\$2.79	70

Part Number Index

www.BradyID.com

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
45363	\$21.84	38	49115	\$94.49	46	50994	\$266.25	190	52066	\$63.59	130
45365	\$21.84	37	49116	\$94.49	46	50995	\$498.32	190	52067	\$63.59	130
45366	\$21.84	37	49117	\$94.49	46	50996	\$321.05	191	52070	\$63.59	225
45367	\$21.84	41	49199	\$72.29	122	50997	\$189.94	192	52073	\$98.30	130
45368	\$21.84	37	49554	\$2.79	70	5100-*	\$8.22	67	52074	\$98.30	130
45370	\$21.84	38	49581	\$2.79	70	51171	\$98.65	205	52075	\$98.30	130
45379	\$34.73	33	49807	\$34.84	39	51172	\$30.78	186	52076	\$98.30	130
45379	\$34.73	33	5000-*	\$28.45	67	51173	\$73.96	186	52077	\$98.30	130
45381	\$49.97	32	50053	\$214.64	62	51181	\$210.41	202	52078	\$98.30	130
45422	\$15.55	37	50054	\$350.07	62	51186	\$190.26	202	52079	\$98.30	130
45470	\$13.19	24	50055	\$144.43	62	51187	\$302.26	202	52086	\$138.81	130
45471	\$23.93	31	50056	\$228.39	62	51188	\$296.53	202	52087	\$138.81	130
45472	\$42.25	24	5010-*	\$5.83	67	51189	\$518.81	202	52090	\$138.81	130
46236	\$299.12	153	50193	\$2.79	226	51194	\$507.32	202	52091	\$138.81	130
46237	\$299.12	153	50194	\$22.56	224	51195	\$828.43	202	52093	\$138.81	130
46347	\$4.14	70	50198	\$39.43	195	51196	\$807.74	202	52094	\$138.81	130
46464	\$11.87	25	50199	\$39.43	195	51252	\$24.49	215	52096	\$138.81	130
46643	\$11.87	25	50250	\$20.19	195	51254	\$24.49	215	52148	\$124.66	131
46674	\$19.74	25	50269	\$9.81	225	51256	\$8.54	215	52149	\$186.45	131
46735	\$19.74	25	50276	\$21.77	224	51258	\$10.98	215	52150	\$186.45	131
46741	\$19.74	25	50280	\$6.96	201	51260	\$45.35	215	52152	\$208.92	131
46748	\$19.74	25	50281	\$6.96	201	51263	\$78.25	215	52153	\$98.30	131
46754	\$19.74	25	50283	\$6.96	201	51264	\$20.27	217	52155	\$173.52	131
46819	\$19.74	25	50289	\$6.96	201	51265	\$24.07	217	52156	\$196.67	131
46990	\$23.93	43	50292	\$6.96	201	51279	\$70.99	200	52157	\$196.67	131
47000	\$15.88	26	50293	\$6.96	201	51280	\$70.99	200	52158	\$161.96	131
47002	\$23.93	26	5050-*	\$6.34	67	51281	\$70.99	200	52203	\$266.46	67
47004	\$23.93	26	50688	\$21.71	37	51282	\$70.99	200	52207	\$294.70	67
47005	\$23.93	31	50692	\$21.71	37	51283	\$70.99	200	52211	\$378.73	67
47008	\$23.93	24	50693	\$28.57	37	51290	\$90.44	200	52215	\$516.20	67
47010	\$23.93	43	50694	\$37.70	37	51292	\$90.44	200	53072	\$312.51	62
47014	\$23.93	26	50696	\$22.80	37	51297	\$90.44	200	53119	\$33.83	52
47018	\$23.93	30	50698	\$37.70	37	51298	\$90.44	200	53200	\$33.83	52
47022	\$23.93	41	50778	\$69.83	37	51299	\$90.44	200	53201	\$33.83	52
47034	\$16.71	33	50784	\$69.83	37	51339	\$79.41	199	53202	\$58.05	53
47035	\$16.71	33	50786	\$69.83	37	51344	\$79.41	199	55260	\$43.58	81
47039	\$11.30	36	50899	\$49.29	212	51345	\$79.41	199	55261	\$43.58	81
47040	\$13.19	33	50900	\$291.25	54	51346	\$79.41	199	55262	\$43.58	81
47044	\$23.93	38	50901	\$291.25	54	51347	\$79.41	199	55263	\$43.58	81
47050	\$23.93	30	50902	\$291.25	54	51353	\$79.41	199	55292	\$39.86	94
47061	\$13.19	30	50903	\$291.25	54	51360	\$90.44	201	55293	\$55.27	94
47093	\$23.93	25	50904	\$291.25	54	51361	\$90.44	201	55296	\$39.86	94
47101	\$23.93	44	50905	\$291.25	54	51362	\$90.44	201	55297	\$55.27	94
47113	\$23.93	30	50906	\$291.25	54	51368	\$90.44	201	55300	\$20.18	94
47117	\$23.93	29	50907	\$291.25	54	51369	\$90.44	201	55301	\$30.18	94
47152	\$13.19	24	50908	\$291.25	54	51370	\$96.93	201	55302	\$39.86	94
47160	\$13.19	41	50909	\$291.25	54	51371	\$96.93	201	55303	\$55.27	94
47171	\$13.19	43	50910	\$291.25	54	51376	\$96.93	201	55312	\$30.18	94
47192	\$23.93	41	50911	\$291.25	54	51377	\$96.93	201	55313	\$39.86	94
47203	\$23.93	43	50912	\$291.25	54	51378	\$96.93	201	55314	\$55.27	94
47206	\$23.93	28	50914	\$281.73	45	51379	\$6.96	201	55324	\$85.69	96
47239	\$43.51	99	50924	\$43.12	212	51388	\$89.99	212	55325	\$148.43	96
47243	\$43.51	99	50932	\$22.13	212	51390	\$83.83	212	55326	\$256.82	96
47288	\$23.93	33	50937	\$71.05	206	51392	\$87.54	212	55327	\$344.48	96
47327	\$23.93	25	50938	\$50.74	206	51394	\$81.38	212	55332	\$296.69	96
47329	\$23.93	49	50939	\$7.56	206	51395	\$19.69	212	55338	\$148.43	96
47330	\$23.93	25	50940	\$41.74	211	5140-*	\$11.14	67	55350	\$296.69	96
47332	\$23.93	44	50941	\$50.62	210	51442	\$41.74	211	55352	\$20.37	96
47334	\$23.93	44	50943	\$47.93	210	51454	\$225.39	227	55353	\$35.91	96
47372	\$46.82	98	50944	\$39.94	210	51455	\$225.39	227	55354	\$60.97	96
47380	\$68.30	98	50945	\$12.64	210	51544	\$547.39	227	55355	\$83.69	96
47382	\$68.30	98	50947	\$10.10	210	51555	\$62.30	36	55356	\$2.35	95
47659	\$4.86	81	50948	\$18.98	210	51556	\$75.06	36	55357	\$2.35	95
47670	\$9.81	46	50950	\$16.44	210	51793	\$637.55	227	55784	\$20.43	50
47676	\$9.81	46	50951	\$25.34	210	5180-*	\$17.14	67	5600-*	\$9.59	80
48111	\$26.94	72	50953	\$21.53	210	52041	\$1,195.00	128	5601-*	\$9.59	80
48112	\$36.19	72	50954	\$31.69	210	52042	\$110.05	130	5602-*	\$9.59	80
48983	\$11.87	26	50956	\$25.34	210	52044	\$110.05	130	5603-*	\$9.59	80
49041	\$15.55	38	50961	\$66.92	228	52045	\$110.05	130	5609-*	\$9.59	80
49044	\$22.11	38	50962	\$72.27	228	52047	\$110.05	130	5614-*	\$9.59	80
49058	\$34.84	39	50979	\$36.95	186	52059	\$110.05	130	5625-*	\$9.59	80
49060	\$34.84	39	50989	\$96.72	202	52060	\$63.59	130	5631-*	\$23.21	80
49061	\$41.84	39	50990	\$120.90	202	52062	\$63.59	130	5634-*	\$23.21	80
49064	\$34.84	39	50991	\$181.38	202	52063	\$63.59	130	5636-*	\$23.21	80
49111	\$94.49	46	50992	\$241.86	202	52064	\$63.59	130	5637-*	\$23.21	80
49112	\$94.49	46	50993	\$431.76	190	52065	\$63.59	130	5643-*	\$23.21	80

Part Number Index

www.BradyID.com

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
65505	\$65.50	195	65974	\$78.77	209	70220	\$23.93	24	7128*	\$2.33	78
65506	\$65.50	195	65975	\$78.77	209	70223	\$23.93	49	71293	\$23.93	24
65515	\$65.50	195	66004	\$12.99	225	70230	\$42.25	49	7129*	\$2.33	78
65520	\$65.50	195	66005	\$15.27	225	70240	\$23.93	28	7130*	\$2.33	78
65521	\$65.50	195	66006	\$12.99	225	70248	\$13.19	30	7137*	\$2.33	78
65522	\$65.50	195	66007	\$15.27	225	70249	\$23.93	30	71389	\$23.93	24
65523	\$65.50	195	66008	\$12.99	225	70258	\$23.93	28	71425	\$23.93	31
65524	\$65.50	195	66009	\$15.27	225	7025*	\$2.33	78	71432	\$42.25	31
65525	\$65.50	195	66050	\$39.43	195	70266	\$23.93	28	71463	\$13.19	31
65526	\$65.50	195	66051	\$39.43	195	70302	\$23.93	44	7146*	\$2.33	78
65527	\$65.50	195	66052	\$39.43	195	70317	\$23.93	29	7147*	\$2.33	78
65534	\$65.50	195	66053	\$39.43	195	70338	\$13.19	44	7148*	\$2.33	78
65535	\$65.50	195	66054	\$39.43	195	70339	\$23.93	44	7149*	\$2.33	78
65555	\$29.51	227	66055	\$39.43	195	70356	\$23.93	29	71545	\$23.93	31
65560	\$17.21	213	66056	\$39.43	195	70358	\$23.93	45	71565	\$13.19	31
65561	\$28.86	213	66060	\$39.43	195	70372	\$23.93	28	71580	\$42.25	24
65562	\$34.56	213	66061	\$39.43	195	70373	\$23.93	28	7163*	\$2.33	78
65563	\$43.28	213	66062	\$39.43	195	70374	\$23.93	29	71649	\$13.19	36
65564	\$83.96	213	66063	\$39.43	195	70375	\$23.93	24	71655	\$15.10	36
65570	\$23.93	41	66064	\$39.43	195	70423	\$42.25	28	7175*	\$2.33	78
65571	\$13.19	225	66065	\$39.43	195	70426	\$10.91	46	7179*	\$2.33	78
65585	\$17.21	213	66066	\$39.43	195	7045*	\$2.33	78	7184*	\$2.33	78
65586	\$28.86	213	66067	\$39.43	195	70466	\$23.93	30	7186*	\$2.33	78
65587	\$34.56	213	66219	\$29.08	226	7046*	\$2.33	78	7190*	\$2.33	78
65588	\$43.28	213	66255	\$547.39	227	70470	\$23.93	41	7196*	\$2.33	78
65589	\$83.96	213	66320	\$56.93	216	70475	\$23.93	45	7198*	\$2.33	78
65590	\$17.21	213	66321	\$10.36	216	7047*	\$2.33	78	7200*	\$2.33	78
65591	\$28.86	213	66328	\$33.10	191	70528	\$23.93	44	72022	\$13.19	43
65592	\$34.56	213	69005	\$42.25	29	70536	\$23.93	49	72024	\$23.93	43
65593	\$43.28	213	69023	\$42.25	31	7054*	\$2.33	78	7203*	\$2.33	78
65594	\$83.96	213	69024	\$42.25	31	7055*	\$2.33	78	7203*	\$2.33	78
65595	\$17.21	213	69025	\$23.93	31	70577	\$20.45	41	72040	\$13.19	43
65596	\$28.86	213	69028	\$20.45	41	7058*	\$2.33	78	7208*	\$2.33	78
65597	\$34.56	213	69035	\$23.93	31	70593	\$10.91	46	72091	\$42.25	43
65598	\$43.28	213	69041	\$23.93	44	7059*	\$2.33	78	7209*	\$2.33	78
65599	\$83.96	213	69042	\$23.93	29	70602	\$23.93	25	7210*	\$2.33	78
65645	\$118.23	222	69043	\$23.93	28	7060*	\$2.33	78	72118	\$23.93	43
65666	\$25.20	213	69074	\$23.93	36	7061*	\$2.33	78	7212*	\$2.33	78
65669	\$41.42	213	69096	\$23.93	24	7062*	\$2.33	78	72148	\$23.93	43
65670	\$65.50	195	69097	\$23.93	24	7063*	\$2.33	78	72155	\$42.25	43
65671	\$65.50	195	69101	\$23.93	24	7065*	\$2.33	78	72176	\$23.93	43
65673	\$19.73	219	69103	\$23.93	25	70667	\$23.93	25	7218*	\$2.33	78
65674	\$15.44	219	69190	\$17.22	31	7067*	\$2.33	78	72230	\$23.93	28
65675	\$18.69	219	69193	\$23.93	24	7068*	\$2.33	78	72246	\$23.93	28
65688	\$27.86	216	69199	\$23.93	33	7069*	\$2.33	78	7224*	\$2.33	78
65690	\$28.08	220	69232	\$20.45	38	7070*	\$2.33	78	72255	\$42.25	43
65691	\$56.12	220	69243	\$11.30	36	7071*	\$2.33	78	7227*	\$2.33	78
65692	\$28.50	213	69264	\$20.45	29	70736	\$13.19	24	72293	\$13.19	43
65693	\$41.86	213	69275	\$23.93	28	7073*	\$2.33	78	72295	\$42.25	43
65695	\$29.44	219	69291	\$42.25	29	70833	\$23.93	24	7229*	\$2.33	78
65696	\$61.23	220	69308	\$20.45	29	7084*	\$2.33	78	72336	\$23.93	43
65699	\$88.84	205	69407	\$23.93	29	7086*	\$2.33	78	72355	\$8.38	43
65750	\$61.82	220	69408	\$23.93	29	7087*	\$2.33	78	7235*	\$2.33	78
65751	\$63.64	220	69409	\$20.45	29	70885	\$13.19	24	72397	\$19.74	43
65780	\$50.07	186	69444	\$23.93	42	7088*	\$2.33	78	72399	\$13.90	43
65810	\$130.02	215	69477	\$23.93	25	7089*	\$2.33	78	72408	\$23.93	28
65814	\$30.68	215	69541	\$23.93	41	7090*	\$2.33	78	7242*	\$2.33	78
65815	\$130.02	215	69551	\$20.45	44	70915	\$13.19	33	7244*	\$2.33	78
65817	\$23.93	30	69562	\$20.45	49	70949	\$23.93	33	72473	\$23.93	28
65903	\$98.10	60	69765	\$23.93	28	70998	\$15.55	37	7247*	\$2.33	78
65937	\$30.56	60	69810	\$38.06	26	71015	\$13.19	33	7250*	\$2.33	78
65948	\$13.19	30	7005*	\$2.33	78	71016	\$23.93	33	7251*	\$2.33	78
65949	\$11.53	30	7006*	\$2.33	78	7107*	\$2.33	78	7252*	\$2.33	78
65950	\$8.38	30	7007*	\$2.33	78	7110*	\$2.33	78	7253*	\$2.33	78
65960	\$78.77	209	70102	\$46.84	26	71118	\$42.25	41	72546	\$13.19	29
65961	\$78.77	209	70103	\$46.84	26	7115*	\$2.33	78	7267*	\$2.33	78
65962	\$78.77	209	70109	\$46.84	26	71178	\$13.19	49	7268*	\$2.33	78
65963	\$78.77	209	7010*	\$2.33	78	7119*	\$2.33	78	7269*	\$2.33	78
65964	\$78.77	209	70110	\$46.84	26	71216	\$42.25	24	72700	\$23.93	38
65965	\$56.93	216	70115	\$34.29	26	7121*	\$2.33	78	7270*	\$2.33	78
65966	\$62.83	216	70123	\$42.18	26	71229	\$42.25	24	72722	\$13.19	38
65967	\$78.77	209	70129	\$46.84	26	7122*	\$2.33	78	7273*	\$2.33	78
65968	\$36.12	219	70141	\$34.29	26	7123*	\$2.33	78	7274*	\$2.33	78
65970	\$78.77	209	7014*	\$2.33	78	7125*	\$2.33	78	72800	\$13.19	42
65971	\$78.77	209	7015*	\$2.33	78	7127*	\$2.33	78	7282*	\$2.33	78
65972	\$78.77	209	7018*	\$2.33	78	71282	\$42.25	24	7283*	\$2.33	78
65973	\$78.77	209	70218	\$62.16	49	71288	\$42.25	24	7285*	\$2.33	78

Part Number Index

www.BradyID.com

Part Number Index

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
85483	\$54.04	34	86771	\$51.98	71	87791	\$2.24	41	90018	\$44.17	40
85484	\$23.74	34	86776	\$51.98	71	87792	\$2.24	41	90019	\$39.86	94
85523	\$54.04	34	86779	\$51.98	71	87795	\$2.24	43	90102	\$13.64	34
85553	\$8.38	28	86781	\$51.98	71	87807B	\$88.14	35	90105	\$13.64	34
85599	\$11.53	42	86783	\$10.93	70	87808B	\$88.14	35	90106	\$13.64	34
85720	\$8.38	42	86793	\$10.93	70	87982	\$230.54	51	90155	\$13.64	34
85724	\$11.53	42	86799	\$10.93	70	88101	\$8.38	41	90156	\$13.64	34
85797	\$8.38	41	86860	\$10.93	70	88102	\$11.53	41	90157	\$27.64	34
85849	\$11.53	41	86861	\$10.93	70	88108	\$11.53	41	90158	\$13.64	34
85858	\$8.38	41	86868	\$10.93	70	88132	\$11.53	41	90159	\$13.64	34
85859	\$11.53	41	87028	\$96.18	64	88172	\$2.24	41	90160	\$13.64	34
85860	\$8.38	41	87600	\$33.67	74	88183	\$8.38	41	90183	\$27.64	34
85890	\$2.24	41	87601	\$33.67	74	88185	\$8.38	41	90367	\$8.20	36
85891	\$4.35	41	87602	\$33.67	74	88186	\$11.53	41	90369	\$32.29	36
85893	\$11.53	41	87603	\$33.67	74	88189	\$8.38	41	90372	\$8.38	36
85972	\$11.53	41	87604	\$33.67	74	88288	\$8.38	41	90383	\$11.53	36
85985	\$8.38	41	87605	\$33.67	74	88302	\$1.58	225	90494	\$27.64	34
86009	\$8.38	46	87606	\$33.67	74	88303	\$1.58	225	90495	\$54.04	34
86015	\$8.38	46	87607	\$50.59	74	88304	\$1.58	41	90496	\$128.26	223
86034	\$11.53	29	87608	\$50.59	74	88327	\$8.38	41	90518	\$27.64	34
86090	\$11.53	36	87609	\$50.59	74	88360	\$11.53	28	90520	\$27.64	34
86091	\$11.53	36	87610	\$50.59	74	88370	\$8.38	43	90521	\$27.64	34
86199	\$10.93	224	87611	\$50.59	74	88371	\$11.53	43	90522	\$27.64	34
86203	\$10.93	70	87612	\$50.59	74	88376	\$8.38	43	90550	\$13.64	34
86204	\$10.93	70	87613	\$50.59	74	88377	\$11.53	43	90592	\$13.64	34
86216	\$10.93	224	87614	\$33.67	74	88378	\$8.38	43	90616	\$27.64	34
86240	\$10.93	224	87615	\$33.67	74	88379	\$11.53	43	90619	\$27.64	34
86245	\$10.93	224	87616	\$33.67	74	88381	\$11.53	43	90620	\$27.64	34
86246	\$10.93	224	87617	\$33.67	74	88412	\$11.53	43	90622	\$27.64	34
86248	\$10.93	225	87618	\$33.67	74	88413	\$8.38	43	90623	\$27.64	34
86250	\$10.93	225	87619	\$33.67	74	88418	\$8.20	43	90628	\$54.04	34
86336	\$163.26	51	87620	\$33.67	74	88421	\$4.59	43	90631	\$54.04	34
86337	\$7.59	51	87627	\$33.67	74	88423	\$8.38	43	90632	\$54.04	34
86339	\$127.53	51	87628	\$33.67	74	88424	\$11.53	43	90634	\$54.04	34
86345	\$226.70	51	87629	\$33.67	74	88426	\$11.53	43	90635	\$54.04	34
86403	\$22.26	71	87630	\$33.67	74	88427	\$8.38	43	90667	\$11.53	27
86418	\$22.26	71	87631	\$33.67	74	88428	\$11.53	43	90674	\$11.53	27
86437	\$22.26	71	87632	\$50.59	74	88452	\$11.53	43	90686	\$23.74	34
86441	\$22.26	71	87633	\$50.59	74	88453	\$8.38	43	90687	\$23.74	34
86442	\$22.26	71	87634	\$50.59	74	88468	\$11.53	43	90690	\$23.74	34
86446	\$22.26	71	87635	\$50.59	74	88472	\$11.53	43	90691	\$23.74	34
86452	\$22.26	72	87636	\$50.59	74	88475	\$8.38	45	90714	\$23.74	34
86453	\$22.26	72	87637	\$50.59	74	88479	\$8.38	45	90748	\$54.04	34
86456	\$22.56	72	87638	\$50.59	74	88497	\$10.40	31	90749	\$54.04	34
86457	\$22.56	72	87639	\$50.59	74	88502	\$6.68	38	90751	\$54.04	34
86458	\$22.56	72	87640	\$50.59	74	88504	\$6.68	36	90752	\$54.04	34
86459	\$22.56	72	87641	\$50.59	74	88571	\$8.38	45	90753	\$54.04	34
86517	\$24.16	72	87642	\$50.59	74	88572	\$11.53	45	90777	\$54.04	34
86524	\$15.89	71	87643	\$50.59	74	88584	\$11.53	45	90793	\$11.53	27
86533	\$15.89	71	87692	\$194.26	207	88643	\$8.38	45	90797	\$11.53	27
86537	\$15.89	71	87693	\$80.21	207	88725	\$8.38	45	90799	\$11.53	27
86556	\$15.89	71	87694	\$2.18	74	88739	\$11.53	45	90803	\$11.53	27
86560	\$15.89	71	87694	\$2.18	74	88748	\$8.38	45	90807	\$11.53	27
86572	\$15.89	72	87695	\$2.36	74	88749	\$11.53	45	90809	\$11.53	27
86573	\$15.89	72	87695	\$2.36	74	88750	\$4.59	45	90818	\$11.53	27
86574	\$15.89	72	87696	\$2.18	74	88752	\$4.59	45	90844	\$12.29	218
86611	\$16.63	71	87696	\$2.18	74	88762	\$8.20	45	90845	\$67.81	218
86614	\$16.63	71	87697	\$2.36	74	88918	\$8.38	26	90847	\$12.29	218
86615	\$16.63	71	87697	\$2.36	74	88919	\$11.53	26	90848	\$67.81	218
86620	\$16.63	71	87698	\$2.18	74	88922	\$2.91	26	90850	\$12.29	218
86624	\$16.63	71	87698	\$2.18	74	88925	\$8.38	26	90851	\$67.81	218
86625	\$16.63	71	87699	\$2.36	74	88926	\$11.53	26	90853	\$12.29	218
86634	\$51.98	71	87699	\$2.36	74	88932	\$8.38	26	90854	\$67.81	218
86643	\$51.98	71	87710	\$2.18	74	88933	\$11.53	26	90891	\$25.34	217
86666	\$51.98	71	87710	\$2.18	74	88947	\$10.22	26	90892	\$18.98	217
86682	\$51.98	72	87711	\$2.36	74	88948	\$6.85	26	90893	\$18.98	217
86684	\$51.98	72	87711	\$2.36	74	88949	\$10.22	26	90920	\$23.74	34
86740	\$51.98	71	87712	\$2.18	74	89112	\$0.90	45	90944	\$23.74	34
86742	\$51.98	71	87712	\$2.18	74	89152	\$1.52	31	90947	\$23.74	34
86745	\$51.98	71	87713	\$2.36	74	89153	\$1.52	31	90948	\$23.74	34
86750	\$51.98	71	87713	\$2.36	74	89156	\$4.59	33	90971	\$76.19	93
86751	\$51.98	71	87748	\$2.24	30	89169	\$2.24	28	90972	\$93.78	93
86756	\$51.98	71	87751	\$2.24	24	89170	\$2.24	28	90973	\$76.19	93
86757	\$51.98	71	87755	\$2.24	24	89173	\$1.58	31	90974	\$93.78	93
86758	\$51.98	71	87768	\$2.24	30	89256	\$30.68	215	91083	\$40.45	97
86761	\$51.98	71	87788	\$2.24	41	89257	\$64.76	63	91084	\$40.45	97

Part Number Index

www.BradyID.com

Part Number Index

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
91100	\$77.93	97	92270	\$324.37	98	95149	\$94.56	100	9714*	\$102.01	67
91102	\$77.93	97	92280	\$43.12	99	95150	\$92.73	100	97198	\$37.50	66
91104	\$77.93	97	92281	\$43.12	99	95155	\$92.73	100	97199	\$42.87	66
91165	\$1.08	154	92285	\$43.12	99	95166	\$207.35	100	97204	\$35.47	51
91166	\$1.26	154	92289	\$43.12	225	95167	\$218.67	100	97205	\$50.78	51
91172	\$8.85	97	92404	\$34.84	39	95193	\$48.68	100	97206	\$54.61	51
91173	\$8.85	97	92405	\$34.84	39	95195	\$48.68	100	97207	\$42.45	51
91175	\$8.85	97	92406	\$34.84	39	95196	\$48.68	100	97208	\$49.36	51
91176	\$25.78	97	92407	\$34.84	39	95197	\$49.70	100	97209	\$42.45	51
91179	\$25.78	97	92408	\$34.84	39	95229	\$55.40	70	97210	\$49.36	51
91200	\$33.36	97	93242	\$2.33	81	95247	\$13.90	25	97211	\$11.96	51
91201	\$63.13	97	93247	\$2.33	81	95255	\$11.87	25	97602	\$52.23	66
91212	\$33.36	97	93257	\$2.33	81	95256	\$9.81	25	97603	\$52.23	66
91224	\$33.36	97	93390	\$4.74	81	95277	\$20.45	29	97609	\$34.84	39
91230	\$55.74	225	93396	\$4.74	81	95278	\$23.93	25	97610	\$34.84	39
91231	\$55.74	225	94008	\$66.91	37	95284	\$20.45	25	97611	\$34.84	39
91256	\$33.36	97	94022	\$66.91	37	95287	\$20.45	31	97613	\$34.84	39
91257	\$63.13	97	94027	\$66.91	37	95318	\$19.74	25	97614	\$34.84	39
91287	\$108.11	81	94029	\$66.91	37	95363	\$19.74	24	97615	\$34.84	39
91288	\$108.11	81	94044	\$38.57	37	95372	\$13.90	24	97738	\$255.76	144
91289	\$108.11	81	94105	\$33.47	49	95373	\$23.93	24	97739	\$174.98	144
91290	\$108.11	81	94116	\$44.17	49	95380	\$19.74	24	97740	\$121.12	144
91295	\$68.88	99	94119	\$44.17	49	95410	\$13.90	46	97741	\$80.73	144
91296	\$115.97	99	94120	\$44.17	49	95411	\$13.90	46	97742	\$255.76	144
91297	\$115.97	99	94130	\$44.17	49	95414	\$13.90	46	97743	\$174.98	144
91298	\$115.97	99	94142	\$63.75	48	95415	\$13.90	46	97744	\$121.12	144
91326	\$22.77	40	94143	\$111.61	48	95419	\$13.90	46	97745	\$80.73	144
91332	\$14.52	40	94144	\$159.47	48	95421	\$13.90	46	98168	\$27.64	99
91333	\$24.11	40	94145	\$231.93	48	95424	\$13.90	46	98859	\$43.61	75
91334	\$33.47	40	94148	\$87.18	48	95444	\$13.90	40	99162	\$86.30	187
91336	\$33.47	40	94150	\$159.47	48	95448	\$13.90	40	99219	\$336.57	145
91351	\$44.17	40	94152	\$106.59	48	95452	\$62.16	46	99220	\$215.37	145
91352	\$44.17	40	94163	\$111.61	49	95458	\$42.25	24	99221	\$134.59	145
91356	\$44.17	40	94174	\$32.29	40	95463	\$42.25	46	99287	\$21.42	69
91357	\$44.17	40	94175	\$44.17	40	95465	\$13.90	46	99289	\$73.55	60
91358	\$32.29	40	94181	\$63.75	48	95466	\$13.90	46	99290	\$75.46	182
91360	\$44.17	40	94185	\$63.75	48	95468	\$13.90	46	99292	\$74.33	182
91362	\$44.17	40	94190	\$84.66	48	95470	\$13.90	46	99293	\$75.21	182
91363	\$44.17	40	94192	\$111.61	49	95481	\$34.10	46	99296	\$106.47	182
91387	\$22.77	40	94195	\$84.66	48	95491	\$34.10	46	99297	\$105.30	182
91409	\$108.11	81	94197	\$84.66	48	95494	\$34.10	46	99300	\$78.42	182
91410	\$108.11	81	94199	\$84.66	48	95496	\$34.10	46	99302	\$109.67	182
91412	\$27.07	81	94209	\$84.66	48	95500	\$13.90	42	99303	\$108.50	182
91413	\$27.07	81	94210	\$84.66	48	95502	\$13.90	46	99305	\$143.64	183
91416	\$54.07	81	94211	\$84.66	48	95503	\$13.90	42	99307	\$174.88	183
91417	\$54.07	81	94212	\$84.66	48	95504	\$19.74	36	99308	\$173.71	183
91418	\$54.07	81	94213	\$84.66	48	95505	\$39.09	36	99310	\$214.38	183
91419	\$54.07	81	94225	\$111.61	48	95635	\$367.28	101	99312	\$244.32	183
91420	\$54.07	81	94234	\$111.61	48	95636	\$360.15	101	99313	\$243.19	183
91421	\$54.07	81	94235	\$159.47	48	95677	\$244.59	101	99320	\$214.81	184
91422	\$54.07	81	94237	\$84.66	48	95678	\$244.59	101	99321	\$246.06	184
91423	\$54.07	81	94240	\$84.66	48	95679	\$244.59	101	99324	\$244.89	184
91424	\$27.07	81	94336	\$9.00	40	95680	\$244.59	101	99458	\$13.32	68
91425	\$27.07	81	95007	\$19.74	29	95681	\$244.59	101	99459	\$13.32	68
91426	\$27.07	81	95036	\$93.11	51	95682	\$244.59	101	99460	\$12.28	68
91427	\$27.07	81	95037	\$93.11	51	95687	\$11.53	31	99461	\$12.28	68
91428	\$21.79	81	95038	\$93.11	51	96060	\$336.57	145	99466	\$13.32	68
91430	\$43.58	81	95039	\$193.05	50	96061	\$215.37	145	99467	\$13.32	68
91450	\$63.13	97	95041	\$193.05	50	96062	\$134.59	145	99468	\$13.32	68
91451	\$63.13	97	95042	\$251.27	50	96222	\$24.16	72	99469	\$13.32	68
91455	\$63.13	97	95043	\$106.36	50	96908	\$22.11	37	99470	\$13.32	68
91600	\$153.48	99	95044	\$164.38	50	96921	\$26.07	96	99471	\$13.32	68
91601	\$153.48	99	95045	\$193.05	50	96922	\$57.02	96	99474	\$13.32	68
91603	\$153.48	99	95046	\$251.27	50	96923	\$57.02	96	99475	\$13.32	68
91606	\$153.48	99	95047	\$28.17	51	96928	\$26.07	96	99476	\$13.32	68
92116	\$74.16	98	95071	\$10.69	101	96929	\$26.07	96	99477	\$13.32	68
92117	\$74.16	98	95073	\$10.69	101	96950	\$26.07	96	99480	\$12.28	68
92118	\$74.16	98	95074	\$10.69	101	96951	\$26.07	96	99481	\$12.28	68
92119	\$422.77	98	95075	\$10.69	101	96952	\$26.07	96	99482	\$12.28	68
92120	\$422.77	98	95137	\$128.26	223	96953	\$26.07	96	99483	\$12.28	68
92121	\$422.77	98	95138	\$128.26	223	96954	\$26.07	96	99484	\$12.28	68
92122	\$105.46	98	95139	\$128.26	223	96955	\$26.07	96	99485	\$12.28	68
92123	\$611.01	98	95141	\$92.73	100	96957	\$26.07	96	99486	\$12.28	68
92125	\$643.98	98	95142	\$12.06	33	97084	\$27.71	96	99487	\$12.28	68
92126	\$105.46	98	95143	\$92.73	100	9712*	\$54.09	67	99488	\$12.28	68
92127	\$611.01	98	95144	\$92.73	100	9713*	\$59.90	67	99489	\$12.28	68

Part Number Index

www.BradyID.com

Part Number Index

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
105041	\$150.00	158	105968	\$111.01	180	113153	\$105.53	144	113253	\$16.54	85
105088	\$2,308.62	128	105969	\$79.32	180	113154	\$65.91	144	113254	\$16.54	85
105089	\$1,845.74	128	105970	\$81.18	180	113155	\$158.77	147	113255	\$22.05	85
105714	\$122.65	207	106434	\$48.07	54	113156	\$158.77	147	113256	\$22.05	85
105715	\$147.20	207	106460	\$67.62	158	113157	\$207.64	147	113257	\$22.05	85
105716	\$171.74	205	106461	\$29.29	158	113158	\$207.64	147	113258	\$22.05	85
105717	\$249.04	205	106462	\$53.66	158	113159	\$207.64	147	113259	\$22.05	85
105718	\$8.54	208	106463	\$74.74	158	113161	\$232.07	147	113260	\$27.56	85
105719	\$9.75	208	106464	\$31.54	158	113162	\$232.07	147	113261	\$27.56	85
105720	\$8.13	208	106465	\$58.96	158	113163	\$232.07	147	113262	\$27.56	85
105721	\$9.29	208	110017	\$439.02	95	113182	\$208.25	130	113263	\$27.56	85
105722	\$2.39	196	110018	\$222.13	95	113183	\$185.10	130	113264	\$27.56	85
105723	\$2.39	196	110019	\$146.60	95	113184	\$145.76	130	113265	\$27.56	85
105724	\$2.39	196	110020	\$74.11	95	113185	\$104.09	130	113266	\$27.56	85
105729	\$23.70	44	110220	\$113.18	147	113186	\$68.22	130	113267	\$27.56	85
105881	\$52.75	201	110221	\$115.34	147	113187	\$208.25	130	113268	\$27.56	85
105882	\$105.51	201	110972	\$19.74	43	113188	\$145.76	130	113269	\$27.56	85
105883	\$105.51	201	110972	\$19.74	43	113189	\$104.09	130	114171	\$79.42	68
105884	\$105.51	201	110973	\$11.87	43	113190	\$68.22	130	114172	\$11.49	68
105885	\$105.51	201	110975	\$9.81	43	113191	\$208.25	130	114173	\$11.49	68
105886	\$43.83	199	110976	\$23.93	43	113192	\$185.10	130	114174	\$79.42	68
105887	\$43.83	199	110977	\$13.19	43	113193	\$145.76	130	114175	\$144.43	68
105888	\$43.83	199	110978	\$8.38	43	113194	\$104.09	130	114176	\$11.58	68
105889	\$43.83	199	110979	\$11.53	43	113195	\$68.22	130	114177	\$144.43	68
105890	\$87.65	199	112500	\$22.77	40	113196	\$208.25	130	114178	\$11.58	68
105891	\$87.65	199	112631	\$204.75	86	113197	\$145.76	130	114447	\$350.00	143
105892	\$87.65	199	112632	\$19.95	86	113198	\$104.09	130	114448	\$600.00	143
105893	\$87.65	199	112633	\$61.95	86	113199	\$68.22	130	114450	\$3,845.00	143
105894	\$49.44	200	113105	\$237.52	144	113200	\$208.25	130	114451	\$4,845.00	143
105895	\$49.44	200	113106	\$158.33	144	113201	\$145.76	130	114452	\$5,345.00	149
105896	\$49.44	200	113107	\$105.53	144	113202	\$104.09	130	114453	\$1,545.00	129
105897	\$49.44	200	113108	\$65.91	144	113203	\$68.22	130	114455	\$4,095.00	143
105898	\$98.90	200	113109	\$237.52	144	113204	\$208.25	130	114456	\$5,095.00	143
105899	\$98.90	200	113110	\$211.12	144	113205	\$145.76	130	114457	\$5,595.00	149
105900	\$98.90	200	113111	\$158.33	144	113206	\$104.09	130	114458	\$1,795.00	129
105901	\$98.90	200	113112	\$105.53	144	113207	\$68.22	130	114533	\$336.57	147
105902	\$52.75	201	113113	\$65.91	144	113208	\$208.25	130	114610	\$20.95	86
105903	\$52.75	201	113114	\$237.52	144	113209	\$145.76	130	114611	\$136.50	86
105904	\$52.75	201	113115	\$211.12	144	113210	\$104.09	130	114612	\$136.50	86
105905	\$23.79	187	113116	\$158.33	144	113211	\$68.22	130	114613	\$178.50	86
105906	\$29.74	187	113117	\$105.53	144	113212	\$208.25	130	114614	\$178.50	86
105909	\$390.84	145	113118	\$65.91	144	113213	\$145.76	130	114635	\$183.50	93
105910	\$250.13	145	113119	\$237.52	144	113214	\$104.09	130	114637	\$40.00	35
105911	\$156.30	145	113120	\$158.33	144	113215	\$68.22	130	114638	\$52.00	35
105912	\$216.35	151	113121	\$105.53	144	113216	\$208.25	130	114639	\$62.00	35
105913	\$299.61	151	113122	\$65.91	144	113217	\$145.76	130	114640	\$40.00	35
105914	\$399.50	151	113123	\$237.52	144	113218	\$208.25	130	114641	\$52.00	35
105928	\$185.22	188	113124	\$158.33	144	113219	\$145.76	130	114642	\$62.00	35
105929	\$176.40	188	113125	\$105.53	144	113220	\$219.27	131	114643	\$56.00	35
105930	\$297.68	188	113126	\$65.91	144	113221	\$219.27	131	114644	\$68.00	35
105931	\$280.04	188	113127	\$237.52	144	113222	\$219.27	131	114645	\$78.00	35
105932	\$88.20	188	113128	\$158.33	144	113225	\$196.12	131	114646	\$56.00	35
105933	\$314.87	189	113129	\$105.53	144	113226	\$196.12	131	114647	\$68.00	35
105934	\$399.22	189	113130	\$65.91	144	113227	\$196.12	131	114648	\$78.00	35
105935	\$390.22	189	113131	\$237.52	144	113228	\$156.78	131	114649	\$30.00	35
105936	\$310.38	189	113132	\$158.33	144	113229	\$156.78	131	114650	\$42.00	35
105937	\$393.60	189	113133	\$105.53	144	113230	\$156.78	131	114651	\$52.00	35
105938	\$384.60	189	113134	\$65.91	144	113231	\$21.41	212	114652	\$30.00	35
105939	\$290.14	189	113135	\$237.52	144	113232	\$21.41	212	114653	\$42.00	35
105940	\$374.47	189	113136	\$158.33	144	113233	\$32.12	212	114654	\$52.00	35
105941	\$365.48	189	113137	\$105.53	144	113234	\$32.12	212	114655	\$30.00	35
105942	\$106.83	187	113138	\$65.91	144	113238	\$1,044.75	87	114656	\$42.00	35
105954	\$262.66	181	113139	\$237.52	144	113239	\$52.45	87	114657	\$52.00	35
105955	\$309.67	181	113140	\$158.33	144	113240	\$31.45	87	114658	\$30.00	35
105956	\$317.68	181	113141	\$105.53	144	113241	\$68.20	87	114659	\$42.00	35
105957	\$202.59	181	113142	\$65.91	144	113242	\$36.70	87	114660	\$52.00	35
105958	\$247.88	181	113143	\$237.52	144	113243	\$36.70	87	114661	\$30.00	35
105959	\$253.85	181	113144	\$158.33	144	113244	\$314.95	87	114662	\$42.00	35
105960	\$178.76	181	113145	\$105.53	144	113245	\$40.79	85	114663	\$52.00	35
105961	\$227.62	181	113146	\$65.91	144	113246	\$40.79	85	114664	\$30.00	35
105962	\$233.04	181	113147	\$237.52	144	113247	\$40.79	85	114665	\$42.00	35
105963	\$107.23	180	113148	\$158.33	144	113248	\$40.79	85	114666	\$52.00	35
105964	\$160.86	180	113149	\$105.53	144	113249	\$40.79	85	114673	\$25.00	35
105965	\$166.83	180	113150	\$65.91	144	113250	\$16.54	85	114674	\$37.00	35
105966	\$71.47	180	113151	\$237.52	144	113251	\$16.54	85	114675	\$47.00	35
105967	\$107.03	180	113152	\$158.33	144	113252	\$16.54	85	114676	\$25.00	35

Part Number Index

www.BradyID.com

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
114677	\$37.00	35	118965	\$36.21	199	141955	\$11.53	43	142297	\$66.19	121
114678	\$47.00	35	118966	\$72.42	199	141956	\$19.74	43	142298	\$99.33	121
114679	\$25.00	35	118967	\$36.21	199	141957	\$11.11	43	142302	\$47.45	121
114680	\$37.00	35	118968	\$72.42	199	141958	\$13.90	43	142303	\$66.19	121
114681	\$47.00	35	118969	\$36.21	199	141959	\$13.19	43	142304	\$99.33	121
114685	\$25.00	35	118970	\$72.42	199	141960	\$8.38	43	142737	\$387.37	152
114686	\$37.00	35	118935	\$65.24	200	141961	\$11.87	43	142738	\$341.25	152
114687	\$47.00	35	118936	\$65.24	200	141962	\$7.51	43	142739	\$271.14	152
114688	\$25.00	35	118937	\$65.24	200	141963	\$9.81	43	142740	\$387.37	152
114689	\$37.00	35	118938	\$65.24	200	141964	\$23.93	43	142741	\$309.88	152
114690	\$47.00	35	118939	\$65.24	200	141965	\$11.53	43	142742	\$387.37	152
114691	\$25.00	35	118940	\$65.24	200	141966	\$19.74	43	142743	\$271.14	152
114692	\$37.00	35	118941	\$81.92	200	141967	\$11.11	43	142744	\$357.67	152
114693	\$47.00	35	118942	\$81.92	200	141968	\$13.90	43	142745	\$309.88	152
114697	\$15.25	35	118943	\$81.92	200	141969	\$42.25	43	142746	\$387.37	152
114898	\$49.95	93	118944	\$81.92	200	141970	\$21.78	43	142747	\$341.25	152
114899	\$469.95	93	118945	\$81.92	200	141971	\$40.34	43	142748	\$271.14	152
114900	\$49.95	93	118946	\$81.92	200	141972	\$19.84	43	142749	\$387.37	152
114901	\$469.95	93	118971	\$46.47	200	141973	\$37.89	43	142750	\$309.88	152
114902	\$39.95	93	118972	\$92.94	200	142109	\$499.95	85	142753	\$387.37	152
114903	\$379.95	93	118973	\$46.47	200	142110	\$999.95	85	142754	\$271.14	152
114904	\$27.95	93	118974	\$92.94	200	142111	\$1,599.95	85	142755	\$387.37	152
114905	\$199.95	93	118975	\$46.47	200	142133	\$64.95	43	142756	\$309.88	152
114906	\$27.95	93	118976	\$92.94	200	142154	\$255.51	90	142757	\$387.37	152
114907	\$199.95	93	118977	\$46.47	200	142155	\$168.05	90	142758	\$271.14	152
114908	\$27.95	93	118978	\$92.94	200	142156	\$321.35	90	142759	\$387.37	152
114909	\$199.95	93	118979	\$46.47	200	142157	\$358.16	90	142760	\$309.88	152
114910	\$27.95	93	118980	\$92.94	200	142158	\$255.51	90	142762	\$271.14	152
114911	\$199.95	93	118981	\$46.47	200	142159	\$168.05	90	142763	\$387.37	152
114912	\$30.95	35	118982	\$92.94	200	142160	\$358.16	90	142764	\$271.14	152
114913	\$30.95	35	141908	\$23.93	26	142161	\$255.51	90	142765	\$387.37	152
114914	\$15.95	35	141909	\$11.53	26	142162	\$168.05	90	142766	\$387.37	152
114915	\$15.95	35	141910	\$19.74	26	142163	\$321.35	90	142767	\$271.14	152
114917	\$19.95	35	141911	\$11.11	26	142164	\$358.16	90	142768	\$387.37	152
114918	\$19.95	35	141912	\$13.90	26	142165	\$255.51	90	142769	\$309.88	152
114919	\$19.95	35	141913	\$13.19	26	142166	\$168.05	90	142770	\$387.37	152
114921	\$19.95	35	141914	\$8.38	26	142167	\$358.16	90	142771	\$271.14	152
115751	\$104.09	130	141915	\$11.87	26	142168	\$255.51	90	142772	\$309.88	152
115752	\$68.22	130	141916	\$7.51	26	142169	\$168.05	90	142773	\$387.37	152
115753	\$104.09	130	141917	\$9.81	26	142170	\$358.16	90	142774	\$387.37	152
115754	\$68.22	130	141919	\$23.93	43	142171	\$255.51	90	142775	\$271.14	152
115755	\$208.25	130	141920	\$11.53	43	142172	\$168.05	90	142776	\$387.37	152
115756	\$145.76	130	141921	\$19.74	43	142173	\$358.16	90	142777	\$309.88	152
115757	\$104.09	130	141922	\$11.11	43	142174	\$255.51	90	142778	\$387.37	152
115758	\$68.22	130	141923	\$13.90	43	142175	\$168.05	90	142779	\$271.14	152
115759	\$208.25	130	141924	\$13.19	43	142176	\$358.16	90	142780	\$387.37	152
115760	\$145.76	130	141925	\$8.38	43	142177	\$63.00	89	142781	\$309.88	152
115761	\$104.09	130	141926	\$11.87	43	142178	\$63.00	89	142782	\$387.37	152
115762	\$68.22	130	141928	\$9.81	43	142179	\$63.00	89	142783	\$271.14	152
115774	\$158.77	147	141928	\$9.81	43	142180	\$63.00	89	142784	\$387.37	152
118925	\$79.41	199	141929	\$23.93	43	142181	\$63.00	89	142785	\$309.88	152
118926	\$63.80	199	141930	\$11.53	43	142269	\$47.45	121	142786	\$271.14	152
118927	\$63.80	199	141931	\$19.74	43	142270	\$66.19	121	142787	\$387.37	152
118928	\$63.80	199	141932	\$11.11	43	142271	\$99.33	121	142788	\$387.37	152
118929	\$63.80	199	141933	\$13.90	43	142272	\$47.45	121	142789	\$271.14	152
118930	\$63.80	199	141934	\$42.25	43	142273	\$66.19	121	142790	\$387.37	152
118931	\$63.80	199	141935	\$21.78	43	142274	\$99.33	121	142791	\$387.37	152
118932	\$63.80	199	141936	\$40.34	43	142275	\$47.45	121	142792	\$271.14	152
118933	\$63.80	199	141937	\$19.84	43	142276	\$66.19	121	142793	\$387.37	152
118934	\$63.80	199	141938	\$37.89	43	142277	\$99.33	121	143123	\$13.50	199
118947	\$43.83	199	141939	\$13.19	43	142278	\$47.45	121	143126	\$11.14	200
118948	\$87.65	199	141940	\$8.38	43	142279	\$66.19	121	143128	\$11.14	200
118949	\$43.83	199	141941	\$11.87	43	142280	\$99.33	121	143130	\$11.14	200
118951	\$43.83	199	141942	\$7.51	43	142281	\$47.45	121	143132	\$11.14	200
118953	\$36.21	199	141943	\$9.81	43	142282	\$66.19	121	143134	\$11.14	200
118954	\$72.42	199	141944	\$23.93	43	142283	\$99.33	121	143136	\$11.14	200
118955	\$36.21	199	141945	\$11.53	43	142284	\$47.45	121	143138	\$13.92	200
118956	\$72.42	199	141946	\$19.74	43	142285	\$66.19	121	143140	\$13.92	200
118957	\$36.21	199	141947	\$11.11	43	142286	\$99.33	121	143142	\$13.92	200
118958	\$72.42	199	141948	\$13.90	43	142287	\$47.45	121	143144	\$13.92	200
118959	\$36.21	199	141949	\$42.25	43	142288	\$66.19	121	143146	\$13.92	200
118960	\$72.42	199	141950	\$21.78	43	142289	\$99.33	121	143148	\$13.92	200
118961	\$36.21	199	141951	\$40.34	43	142290	\$47.45	121	143150	\$10.90	199
118962	\$72.42	199	141952	\$19.84	43	142291	\$66.19	121	143152	\$10.90	199
118963	\$36.21	199	141953	\$37.89	43	142292	\$99.33	121	143154	\$10.90	199
118964	\$72.42	199	141954	\$23.93	43	142296	\$47.45	121	143156	\$10.90	199

Part Number Index

www.BradyID.com

Part #	Price	Pg.
143158	\$10.90	199
143160	\$10.90	199
143162	\$10.90	199
143164	\$10.90	199
143166	\$10.90	199
AW124	\$88.87	167
AW1818	\$103.56	167
AW412	\$88.87	167
AW430	\$142.69	167
AW806	\$88.87	167
AW99	\$123.07	167
B30-17-438	\$116.50	140
B30-18-438	\$174.25	140
B30-25-595-ANSICA	\$221.98	135
B30-25-595-ANSIDA	\$221.98	135
B30-25-595-ANSINO	\$221.98	135
B30-25-595-ANSIWA	\$221.98	135
B30-25-595-BLNKWT	\$221.98	136
B30-25-595-BLNKYL	\$221.98	136
B30-25-595-OSHACA	\$221.98	135
B30-25-595-OSHADA	\$221.98	135
B30-161-595-NFPA	\$232.07	135
B30-179-427	\$157.45	138
B30-188-427	\$146.95	138
B30-219-595-BLNKWT	\$98.91	136
B30-222-438	\$174.25	140
B30-223-427	\$178.45	138
B30-224-427	\$146.95	138
B30-225-427	\$146.95	138
B30-255-551-ANSICA	\$169.88	136
B30-255-551-OSHADA	\$169.88	136
B30-226-427	\$146.95	138
B30-227-427	\$178.45	138
B30-228-427	\$89.20	138
B30-229-427	\$89.20	138
B30-231-427	\$89.20	138
B30-232-427	\$89.20	138
B30-233-427	\$178.45	138
B30-234-427	\$146.95	138
B30-241-595-ANSICA	\$147.97	135
B30-241-595-ANSIDA	\$147.97	135
B30-241-595-ANSINO	\$147.97	135
B30-241-595-ANSIWA	\$147.97	135
B30-241-595-BLNKWT	\$142.89	136
B30-241-595-BLNKYL	\$142.89	136
B30-241-595-OSHACA	\$147.97	135
B30-241-595-OSHADA	\$147.97	135
B30-242-595-BLNKWT	\$98.91	136
B30-243-595-CB	\$232.07	135
B30-243-595-NFPA	\$232.07	135
B30-244-595-CB	\$158.77	135
B30-244-595-DIAM	\$158.77	135
B30-244-595-HMIG	\$158.77	135
B30-244-595-NFPA	\$158.77	135
B30-245-595-CB	\$158.77	135
B30-245-595-NFPA	\$158.77	135
B30-246-595-HMIG	\$109.90	135
B30-246-595-NFR	\$109.90	135
B30-255-551-ANSID	\$169.88	136
B30C-255-551-WHT	\$169.88	136
B30C-500-569-BK	\$73.25	134
B30C-500-569-BL	\$73.25	134
B30C-500-569-BR	\$73.25	134
B30C-500-569-CL	\$73.25	134
B30C-500-569-GN	\$73.25	134
B30C-500-569-GY	\$73.25	134
B30C-500-569-LB	\$73.25	134
B30C-500-569-OC	\$73.25	134
B30C-500-569-OR	\$73.25	134
B30C-500-569-PK	\$73.25	134
B30C-500-569-PL	\$73.25	134
B30C-500-569-RD	\$73.25	134
B30C-500-569-SB	\$73.25	134
B30C-500-569-TN	\$73.25	134
B30C-500-569-WT	\$73.25	134
B30C-500-569-YL	\$73.25	134

Part #	Price	Pg.
B30C-500-581-WT	\$61.60	137
B30C-500-581-YL	\$61.60	137
B30C-500-595-BK	\$61.60	134
B30C-500-595-BL	\$61.60	134
B30C-500-595-BR	\$61.60	134
B30C-500-595-CL	\$61.60	134
B30C-500-595-GD	\$61.60	134
B30C-500-595-GN	\$61.60	134
B30C-500-595-GY	\$61.60	134
B30C-500-595-OR	\$61.60	134
B30C-500-595-PL	\$61.60	134
B30C-500-595-RD	\$61.60	134
B30C-500-595-SL	\$61.60	134
B30C-500-595-WT	\$61.60	134
B30C-1125-526	\$141.82	138
B30C-1125-549-WT	\$109.90	137
B30C-1125-549-YL	\$109.90	137
B30C-1125-565-SL	\$122.12	140
B30C-1125-569-BK	\$109.90	134
B30C-1125-569-BL	\$109.90	134
B30C-1125-569-BR	\$109.90	134
B30C-1125-569-CL	\$109.90	134
B30C-1125-569-GN	\$109.90	134
B30C-1125-569-GY	\$109.90	134
B30C-1125-569-LB	\$109.90	134
B30C-1125-569-OC	\$109.90	134
B30C-1125-569-OR	\$109.90	134
B30C-1125-569-PK	\$109.90	134
B30C-1125-569-PL	\$109.90	134
B30C-1125-569-RD	\$109.90	134
B30C-1125-569-SB	\$109.90	134
B30C-1125-569-TN	\$109.90	134
B30C-1125-569-WT	\$109.90	134
B30C-1125-569-YL	\$109.90	134
B30C-1125-581-WT	\$98.63	137
B30C-1125-581-YL	\$98.63	137
B30C-1125-584-OR	\$122.12	138
B30C-1125-584-SL	\$122.12	138
B30C-1125-584-YL	\$122.12	138
B30C-1125-595-BK	\$98.63	134
B30C-1125-595-BL	\$98.63	134
B30C-1125-595-BR	\$98.63	134
B30C-1125-595-CL	\$98.63	134
B30C-1125-595-GD	\$98.63	134
B30C-1125-595-GN	\$98.63	134
B30C-1125-595-GY	\$98.63	134
B30C-1125-595-OR	\$98.63	134
B30C-1125-595-PL	\$98.63	134
B30C-1125-595-RD	\$98.63	134
B30C-1125-595-WT	\$98.63	134
B30C-1125-595-YL	\$98.63	134
B30C-2250-526	\$226.95	138
B30C-2250-549-WT	\$158.77	137
B30C-2250-549-YL	\$158.77	137
B30C-2250-565-SL	\$195.42	140
B30C-2250-569-BK	\$158.77	134
B30C-2250-569-BL	\$158.77	134
B30C-2250-569-BR	\$158.77	134
B30C-2250-569-CL	\$158.77	134
B30C-2250-569-GN	\$158.77	134
B30C-2250-569-GY	\$158.77	134
B30C-2250-569-LB	\$158.77	134
B30C-2250-569-OC	\$158.77	134
B30C-2250-569-OR	\$158.77	134
B30C-2250-569-PK	\$158.77	134
B30C-2250-569-PL	\$158.77	134
B30C-2250-569-RD	\$158.77	134
B30C-2250-569-SB	\$158.77	134
B30C-2250-569-TN	\$158.77	134
B30C-2250-569-WT	\$158.77	134
B30C-2250-569-YL	\$158.77	134
B30C-2250-581-WT	\$147.97	137
B30C-2250-581-YL	\$147.97	137
B30C-2250-584-OR	\$195.42	138
B30C-2250-584-SL	\$195.42	138
B30C-2250-584-YL	\$195.42	138

Part #	Price	Pg.
B30C-2250-595-BK	\$147.97	134
B30C-2250-595-BL	\$147.97	134
B30C-2250-595-BR	\$147.97	134
B30C-2250-595-CL	\$147.97	134
B30C-2250-595-GD	\$147.97	134
B30C-2250-595-GN	\$147.97	134
B30C-2250-595-GY	\$147.97	134
B30C-2250-595-OR	\$147.97	134
B30C-2250-595-PL	\$147.97	134
B30C-2250-595-RD	\$147.97	134
B30C-2250-595-WT	\$147.97	134
B30C-2250-595-YL	\$147.97	134
B30C-2500-509-WT	\$91.57	137
B30C-2500-509-YL	\$91.57	137
B30C-2500-551-WT	\$122.12	137
B30C-3000-438-SL	\$195.25	140
B30C-3000-569-WT	\$207.64	134
B30C-3000-595-WT	\$197.31	134
B30C-3000-595-YL	\$197.31	134
B30C-3250-551-WT	\$158.77	137
B30C-3250-551-YL	\$158.77	137
B30C-4000-526	\$354.64	138
B30C-4000-549-WT	\$232.07	137
B30C-4000-549-YL	\$232.07	137
B30C-4000-565-SL	\$305.39	140
B30C-4000-569-BK	\$232.07	134
B30C-4000-569-BL	\$232.07	134
B30C-4000-569-BR	\$232.07	134
B30C-4000-569-CL	\$232.07	134
B30C-4000-569-GN	\$232.07	134
B30C-4000-569-GY	\$232.07	134
B30C-4000-569-LB	\$232.07	134
B30C-4000-569-OC	\$232.07	134
B30C-4000-569-OR	\$232.07	134
B30C-4000-569-PK	\$232.07	134
B30C-4000-569-PL	\$232.07	134
B30C-4000-569-RD	\$232.07	134
B30C-4000-569-SB	\$232.07	134
B30C-4000-569-TN	\$232.07	134
B30C-4000-569-WT	\$232.07	134
B30C-4000-569-YL	\$232.07	134
B30C-4000-581-WT	\$221.98	137
B30C-4000-581-YL	\$221.98	137
B30C-4000-584-OR	\$305.39	138
B30C-4000-584-SL	\$305.39	138
B30C-4000-584-YL	\$305.39	138
B30C-4000-595-BK	\$221.98	134
B30C-4000-595-BL	\$221.98	134
B30C-4000-595-BR	\$221.98	134
B30C-4000-595-CL	\$221.98	134
B30C-4000-595-GD	\$221.98	134
B30C-4000-595-GN	\$221.98	134
B30C-4000-595-GY	\$221.98	134
B30C-4000-595-OR	\$221.98	134
B30C-4000-595-PL	\$221.98	134
B30C-4000-595-RD	\$221.98	134
B30C-4000-595-WT	\$221.98	134
B30C-4000-595-YL	\$221.98	134
B30C-4250-509-WT	\$122.12	137
B30C-4250-509-YL	\$122.12	137
B30EP-167-593-BK	\$143.02	139
B30EP-167-593-GN	\$143.02	139
B30EP-167-593-RD	\$143.02	139
B30EP-167-593-WT	\$143.02	139
B30EP-167-593-YL	\$143.02	139
B30EP-167U-593-BK	\$143.02	139
B30EP-167U-593-GN	\$143.02	139
B30EP-167U-593-RD	\$143.02	139
B30EP-167U-593-WT	\$143.02	139
B30EP-167U-593-YL	\$143.02	139
B30EP-168-593-BK	\$129.92	139
B30EP-168-593-GN	\$129.92	139
B30EP-168-593-RD	\$129.92	139
B30EP-168-593-WT	\$129.92	139
B30EP-168-593-YL	\$129.92	139

Part #	Price	Pg.
B30EP-169-593-BK	\$140.91	139
B30EP-169-593-GN	\$140.91	139
B30EP-169-593-RD	\$140.91	139
B30EP-169-593-WT	\$140.91	139
B30EP-169-593-YL	\$140.91	139
B30EP-170-593-BK	\$135.11	139
B30EP-170-593-GN	\$135.11	139
B30EP-170-593-RD	\$135.11	139
B30EP-170-593-WT	\$135.11	139
B30EP-170-593-YL	\$135.11	139
B30EP-171-593-BK	\$170.60	139
B30EP-171-593-GN	\$170.60	139
B30EP-171-593-RD	\$170.60	139
B30EP-171-593-SL	\$170.60	139
B30EP-171-593-WT	\$170.60	139
B30EP-171-593-YL	\$170.60	139
B30EP-173-593-BK	\$113.00	139
B30EP-173-593-GN	\$113.00	139
B30EP-173-593-RD	\$113.00	139
B30EP-173-593-SL	\$113.00	139
B30EP-173-593-WT	\$113.00	139
B30EP-173-593-YL	\$113.00	139
B30EP-174-593-BK	\$233.37	139
B30EP-174-593-GN	\$233.37	139
B30EP-174-593-RD	\$233.37	139
B30EP-174-593-SL	\$233.37	139
B30EP-174-593-WT	\$233.37	139
B30EP-174-593-YL	\$233.37	139
B30EP-175-593-BK	\$267.49	139
B30EP-175-593-GN	\$267.49	139
B30EP-175-593-WT	\$267.49	139
B30EP-175-593-YL	\$267.49	139
B30EP-176-593-BK	\$233.37	139
B30EP-176-593-GN	\$233.37	139
B30EP-176-593-RD	\$233.37	139
B30EP-176-593-SL	\$233.37	139
B30EP-176-593-WT	\$233.37	139
B30EP-176-593-YL	\$233.37	139
B30EP-177-593-BK	\$159.27	139
B30EP-177-593-GN	\$159.27	139
B30EP-177-593-RD	\$159.27	139
B30EP-177-593-WT	\$159.27	139
B30EP-177-593-YL	\$159.27	139
B30KIT-ARCLASH-W	\$970.00	141
B30KIT-GENIND	\$1,750.00	141
B30KIT-LEANVW	\$1,495.00	141
B30KIT-PIPE	\$1,770.00	141
B30KIT-SFTY	\$1,345.00	141
B30-R10000	\$103.79	140
B30-R10000-BL	\$103.79	140
B30-R10000-GN	\$103.79	140
B30-R10000-OR	\$103.79	140
B30-R10000-RD	\$103.79	140
B30-R10000-WT	\$103.79	140
B30-R10000-YL	\$103.79	140
B30-R4300	\$103.79	140
B30-R6000	\$103.79	140
B31-CCT	\$12.95	132
B31-DC	\$12.95	132
B31-STYLUS	\$12.95	132
B31-WIPER	\$22.95	132
BBP31	\$1,795.00	

Part Number Index

www.BradyID.com

Part Number Index

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
BMP21	\$145.95	116	BMP71-360-KIT	\$1,074.00	104	GD01	\$33.70	102	M21-375-430	\$19.58	116
BMP21-AC	\$42.00	116	BMP71-LM	\$984.60	104	GD02	\$46.35	102	M21-375-499	\$22.11	116
BMP21-HC	\$36.75	116	BMP71-MW	\$1,344.60	104	GD03	\$52.76	102	M21-375-499-TB	\$22.11	116
BMP21-MAGNET	\$15.75	116	BMP71-QC	\$955.00	104	GD03DL	\$95.76	102	M21-375-C-342	\$57.46	116
BMP21-TOOL	\$31.50	116	BMP71-SC	\$920.00	104	GLOBOX	\$96.43	206	M21-375-595-BL	\$20.46	116
BM71-7-423	\$300.36	108	BMP71-SC-QC	\$980.00	104	GP30	\$161.69	164	M21-375-595-GN	\$20.46	116
BM71-11-427	\$260.12	110	BPO100	\$41.66	165	GP100	\$92.08	164	M21-375-595-OR	\$20.46	116
BM71-11-498	\$313.52	109	BPO200	\$58.00	165	GP100-B	\$92.08	164	M21-375-595-RD	\$20.46	116
BM71-11-499	\$321.24	109	BPO500	\$33.00	165	GP200	\$96.03	164	M21-375-595-WT	\$20.46	116
BM71-12-109	\$257.24	112	BPU100	\$47.00	164	GP200-B	\$96.03	164	M21-375-595-YL	\$20.46	116
BM71-16-423	\$297.41	108	BPU200	\$62.00	164	GP300	\$75.00	164	M21-500-423	\$19.39	116
BM71-17-423	\$288.69	108	BPU500	\$37.78	164	GP500	\$56.77	164	M21-500-430	\$19.58	116
BM71-17-427	\$278.19	110	BR801B	\$13.51	59	GS-10	\$2,125.80	168	M21-500-499	\$22.11	116
BM71-18-427	\$227.81	110	BR0150	\$102.00	165	HAZ99	\$129.48	166	M21-500-499-TB	\$22.11	116
BM71-18-498	\$251.62	109	BRU150	\$110.00	164	HAZ100-7	\$227.09	166	M21-500-595-BL	\$20.46	116
BM71-19-423	\$209.69	108	BS07A-BU	\$27.02	213	HAZ124	\$103.31	166	M21-500-595-GN	\$20.46	116
BM71-19-427	\$249.67	110	BS07A-GN	\$27.02	213	HAZ412	\$103.31	166	M21-500-595-OR	\$20.46	116
BM71-19-498	\$272.93	109	BS07A-RD	\$27.02	213	HAZ1818	\$111.09	167	M21-500-595-RD	\$20.46	116
BM71-20-422	\$193.42	112	BS07A-YW	\$27.02	213	HT15	\$137.26	164	M21-500-595-WT	\$20.46	116
BM71-20-423	\$167.42	108	BS08A-BU	\$54.06	213	HT30	\$207.37	164	M21-500-595-YL	\$20.46	116
BM71-21-427	\$191.55	110	BS08A-GN	\$54.06	213	HT153	\$132.81	164	M21-750-423	\$21.54	116
BM71-23-427	\$228.72	110	BS08A-RD	\$54.06	213	HT215	\$93.34	164	M21-750-427	\$27.46	116
BM71-29-423	\$331.92	108	BS08A-YW	\$54.06	213	HT230	\$168.90	164	M21-750-430	\$21.75	116
BM71-29-427	\$340.19	110	BSM100	\$259.46	166	HT303	\$212.18	164	M21-750-499	\$25.00	116
BM71-29-498	\$339.55	109	BSM300	\$696.40	166	HT303X	\$212.18	164	M21-750-595-BL	\$23.70	116
BM71-30-427	\$253.45	110	BSM3650	\$186.88	166	HT350	\$127.15	164	M21-750-595-GN	\$23.70	116
BM71-31-427	\$321.24	110	CABLO	\$27.02	211	HT550	\$38.33	164	M21-750-595-OR	\$23.70	116
BM71-32-427	\$132.15	110	CABLO-10	\$30.80	211	HT555	\$129.72	164	M21-750-595-RD	\$23.70	116
BM71-33-427	\$154.25	110	CC400V	\$72.21	167	IC326E	\$71.55	59	M21-750-595-WT	\$23.70	116
BM71-34-427	\$255.41	110	CH100	\$111.09	166	IDPRO-BC	\$22.05	126	M21-750-595-YL	\$23.70	116
BM71-40-412	\$284.59	112	CH1212	\$120.97	166	IDPRO-BP	\$49.07	126	M21-1000-427	\$33.25	116
BM71-64-427	\$117.29	110	CH15P	\$96.28	166	IDPRO-HC	\$49.07	126	M21-1250-427	\$33.86	116
BM71-75-461	\$245.67	113	CH30DP	\$195.02	166	JS1	\$183.67	59	M21-1500-427	\$34.26	116
BM71-94-175-342	\$1,083.78	111	CL-105-619	\$34.60	127	LOFE15A	\$16.20	37	M420	\$72.00	102
BM71-94-175-342YL	\$1,083.78	111	CL-111-502	\$53.02	127	LABXPRT-SER-USB	\$37.84	120	M71-1-423	\$27.37	108
BM71-107-427	\$384.69	110	CL-111-607	\$56.95	127	LAD-EITH/L12	\$95.70	73	M71-2-423	\$18.35	108
BM71-109-427	\$154.25	110	CL-111-619	\$41.48	127	LAD-EITH12	\$68.36	73	M71-2-477	\$41.70	113
BM71-110-145-GY	\$228.99	111	CL-111-969	\$54.74	127	LAD-EITL521	\$162.75	73	M71-3-423	\$28.54	108
BM71-111-145-GY	\$228.99	111	CL-117-619	\$47.19	127	LC251M	\$414.85	193	M71-3-457	\$97.10	108
BM71-125-1-342	\$338.23	111	CL-311-502	\$65.70	127	LC252M	\$190.73	187	M71-4-423	\$29.87	108
BM71-125-175-342	\$454.43	111	CL-311-619	\$51.14	127	LC254M	\$11.86	187	M71-4-478	\$76.06	113
BM71-125-175-342YL	\$454.43	111	CL-311-969	\$68.68	127	LG003E	\$71.03	206	M71-5-423	\$38.71	108
BM71-187-1-342	\$377.35	111	CL-317-619	\$57.50	127	LG008E	\$76.57	206	M71-6-423	\$40.71	108
BM71-187-1-342YL	\$377.35	111	CL-517-619	\$39.08	127	LG252M	\$107.13	192	M71-6-473	\$51.78	108
BM71-187-175-342	\$491.19	111	CL-917-619	\$48.35	127	LH220A	\$10.98	208	M71-7-423	\$35.81	108
BM71-187-175-342YL	\$491.19	111	105372	\$145.46	196	LH220A-YW	\$9.77	208	M71-7-498	\$49.20	109
BM71-250-1-342	\$456.52	111	105373	\$145.46	196	LK041R	\$111.74	211	M71-7-499	\$50.25	109
BM71-250-175-342	\$614.58	111	CSP	\$31.42	53	LK042R	\$117.00	211	M71-9-423	\$42.95	108
BM71-250-175-342YL	\$614.58	111	DGUARD14	\$172.40	167	LK520B	\$99.85	211	M71-9-426	\$145.50	108
BM71-375-1-342	\$673.71	111	DGUARD1410	\$1,597.92	167	LK980E	\$65.73	193	M71-9-473	\$53.79	108
BM71-375-175-342	\$905.32	111	DGUARD9	\$115.84	167	LK981E	\$393.08	193	M71-9-478	\$116.44	113
BM71-500-1-342	\$778.39	111	DGUARD910	\$1,132.42	167	LKX	\$119.76	193	M71-10-423	\$44.27	108
BM71-500-1-342YL	\$778.39	111	DPE	\$70.69	102	LKX-RACK	\$43.61	193	M71-10-427	\$34.94	110
BM71-500-175-342	\$1,047.15	111	DPA24	\$206.57	169	LKXSET	\$145.96	193	M71-10-457	\$147.14	108
BM71-500-175-342YL	\$1,047.15	111	DPA24	\$206.57	169	LKX-TKLBOX	\$38.98	186	M71-10-473	\$55.36	108
BM71-1000-175-342	\$728.01	111	DTA25	\$111.46	169	LM023E	\$16.57	223	M71-10-498	\$51.28	109
BM71C-125-342	\$212.06	111	DTO25	\$111.46	169	LOCB	\$20.97	228	M71-11-427	\$37.15	110
BM71C-187-342	\$224.91	111	DZ-100	\$627.20	168	LOPADDUSER1	\$695.00	229	M71-11-498	\$44.76	109
BM71C-240-498	\$272.50	109	EHMVSD	\$67.66	102	LOPBASIC3001	\$5,095.00	229	M71-11-499	\$45.80	109
BM71C-250-342	\$289.17	111	ENT-ETSH157	\$85.45	73	LOPCORP2001	\$11,995.00	229	M71-12-109	\$36.77	112
BM71C-318-498	\$279.48	109	ENT-ETSH157A	\$126.46	73	LOPDESK1001	\$795.00	229	M71-13-423	\$47.17	108
BM71C-375-342	\$424.12	111	ENT-ETSI532	\$284.81	73	LOS81	\$18.03	60	M71-13-426	\$142.65	108
BM71C-375-498	\$283.89	109	ENV100	\$76.16	165	LOSC13	\$11.53	226	M71-14-423	\$50.06	108
BM71C-500-342	\$488.38	111	ENV150	\$117.26	165	LOSC13 BI	\$12.50	226	M71-14-477	\$147.14	113
BM71C-1000-342	\$674.73	111	ENV200	\$80.10	165	LOSF5	\$9.27	228	M71-15-423	\$51.52	108
BM71C-1000-582*	\$131.94	114	ENV300	\$62.83	165	LOSP22	\$78.82	60	M71-16-423	\$42.41	108
BM71C-1000-584-OR*	\$131.94	114	ENV50	\$132.32	165	LOSP8	\$25.89	52	M71-16-426	\$159.57	108
BM71C-1000-584-WT*	\$131.94	114	ENV500	\$46.91	165	LOSP8SP	\$25.89	52	M71-16-430	\$46.65	107
BM71C-1000-584-YL*	\$131.94	114	ENV510	\$121.08	168	LR008E	\$104.64	203	M71-16-457	\$159.57	108
BM71C-2000-582	\$211.35	114	ENV810	\$155.40	168	LR018E	\$119.74	203	M71-16-473	\$53.13	108
BM71C-2000-582*	\$211.35	114	EPD	\$70.35	103	LR060E	\$20.77	203	M71-16-483	\$51.66	107
BM71C-2000-584-OR*	\$211.35	114	FESP	\$25.64	53	LR360E	\$32.48	203	M71-16-498	\$53.78	109
BM71C-2000-584-WT*	\$211.35	114	FLSP	\$25.64	53	M21-125-C-342	\$41.72	116	M71-16-499	\$54.96	109
BM71C-2000-584-YL*	\$211.35	114	FLT-ETSH9	\$55.13	73	M21-187-C-342	\$45.52	116	M71-17-351	\$53.79	113
BMP71	\$895.00	104	FLT-ETSH9A	\$126.46	73	M21-250-C-342	\$52.07	116	M71-17-352	\$54.17	113
BMP71-360	\$179.00	104	FLT-ETSI51	\$284.81	73	M21-375-423	\$19.39	116	M71-17-423	\$42.41	108

Part Number Index

www.BradyID.com

Part #	Price	Pg.
M71-17-426	\$163.68	108
M71-17-427	\$39.78	110
M71-17-430	\$46.65	107
M71-17-473	\$53.13	108
M71-17-483	\$52.73	107
M71-17-486	\$58.75	107
M71-17-489	\$51.66	109
M71-17-498	\$56.52	109
M71-18-427	\$32.47	110
M71-18-498	\$37.03	109
M71-18-499	\$37.82	109
M71-19-423	\$29.99	108
M71-19-427	\$35.73	110
M71-19-427-YL	\$39.38	110
M71-19-483	\$37.13	107
M71-19-498	\$40.18	109
M71-19-499	\$41.09	109
M71-20-351	\$33.02	113
M71-20-352	\$33.02	113
M71-20-423	\$23.91	108
M71-20-459	\$25.36	107
M71-20-483	\$28.69	107
M71-20-486	\$36.05	107
M71-21-427	\$27.36	110
M71-21-427-YL	\$34.28	110
M71-21-498	\$32.84	109
M71-21-499	\$38.74	109
M71-22-423	\$28.81	108
M71-23-423	\$34.74	108
M71-23-427	\$32.58	110
M71-23-483	\$43.47	107
M71-24-423-BK	\$41.23	108
M71-25-423	\$54.31	108
M71-25-478	\$146.81	113
M71-26-423	\$34.74	108
M71-27-423	\$55.50	108
M71-28-423	\$61.83	108
M71-28-426	\$187.43	108
M71-28-427	\$44.49	110
M71-28-473	\$77.17	108
M71-28-499	\$53.52	109
M71-29-423	\$47.42	108
M71-29-427	\$48.67	110
M71-29-459	\$47.42	107
M71-29-483	\$58.53	107
M71-29-486	\$67.60	107
M71-29-489	\$57.60	107
M71-29-498	\$49.98	109
M71-29-499	\$51.02	109
M71-30-422	\$49.41	112
M71-30-423-TEST	\$38.71	106
M71-30-427	\$36.25	110
M71-30-427-AW	\$36.25	110
M71-30-427-BL	\$45.28	110
M71-30-427-PL	\$45.28	110
M71-30-427-RD	\$45.28	110
M71-30-428-CALI	\$59.91	106
M71-30-459	\$41.49	107
M71-30-483	\$50.33	107
M71-30-486	\$55.41	107
M71-30-498	\$43.97	109
M71-30-499	\$45.16	109
M71-31-351	\$43.21	113
M71-31-352	\$43.21	113
M71-31-423	\$34.09	108
M71-31-427	\$45.80	110
M71-31-427-GN	\$58.37	110
M71-31-427-RD	\$58.37	110
M71-31-427-YL	\$58.37	110
M71-31-483	\$42.01	107
M71-31-498	\$51.02	109
M71-31-499	\$52.34	109
M71-32-423	\$48.49	108
M71-32-427	\$47.36	110
M71-32-427-YL	\$58.75	110
M71-32-489	\$58.80	107

Part #	Price	Pg.
M71-32-498	\$63.19	109
M71-33-427	\$44.09	110
M71-33-427-YL	\$55.22	110
M71-33-498	\$53.00	109
M71-34-427	\$36.51	110
M71-35-428-PROP	\$59.91	106
M71-36-109	\$49.20	112
M71-37-351	\$47.82	113
M71-37-352	\$47.70	113
M71-37-422	\$41.23	112
M71-37-423	\$34.74	108
M71-37-483	\$42.01	107
M71-37-486	\$51.96	107
M71-38-423	\$41.49	108
M71-38-483	\$50.47	107
M71-38-483-CAUT	\$58.04	106
M71-38-483-DANG	\$58.04	106
M71-38-483-NOTI	\$58.04	106
M71-38-483-WARN	\$58.04	106
M71-38-489	\$50.47	107
M71-40-412	\$61.11	112
M71-45-422	\$52.73	112
M71-45-430	\$48.75	107
M71-61-483	\$18.88	107
M71-64-427	\$16.75	110
M71-65-483	\$32.90	107
M71-66-427	\$44.09	110
M71-68-430	\$32.64	107
M71-71-430	\$32.64	107
M71-78-499	\$65.81	109
M71-80-488	\$26.57	107
M71-81-488	\$65.81	107
M71-81-499	\$62.68	109
M71-82-499	\$33.76	113
M71-83-499	\$33.76	113
M71-84-499	\$47.24	109
M71-88-427	\$61.89	110
M71-94-1-342	\$45.67	111
M71-94-1-342YL	\$46.05	111
M71-94-175-342	\$62.02	111
M71-94-175-342YL	\$62.02	111
M71-96-427	\$25.37	110
M71-97-488	\$28.92	107
M71-98-499	\$66.61	113
M71-103-427	\$42.14	110
M71-104-427	\$45.80	110
M71-107-427	\$56.67	110
M71-109-427	\$44.09	110
M71-110-145FR-GY	\$35.99	111
M71-110-145-GY	\$32.70	111
M71-111-145FR-GY	\$35.99	111
M71-111-145-GY	\$32.70	111
M71-125-1-342	\$48.41	111
M71-125-1-342YL	\$48.41	111
M71-125-175-342	\$65.03	111
M71-125-175-342YL	\$65.03	111
M71-187-1-342	\$53.91	111
M71-187-1-342YL	\$53.91	111
M71-187-175-342	\$72.22	111
M71-187-175-342YL	\$72.22	111
M71-250-1-342	\$65.30	111
M71-250-1-342YL	\$65.30	111
M71-250-175-342	\$87.93	111
M71-250-175-342YL	\$87.65	111
M71-375-1-342	\$96.19	111
M71-375-1-342YL	\$96.19	111
M71-375-175-342	\$129.40	111
M71-375-175-342YL	\$129.40	111
M71-500-1-342	\$111.21	111
M71-500-1-342YL	\$111.21	111
M71-500-175-342	\$149.54	111
M71-500-175-342YL	\$149.54	111
M71-1000-1-342	\$76.82	111
M71-1000-1-342YL	\$76.82	111
M71-1000-175-342	\$104.04	111
M71-1000-175-342YL	\$104.04	111

Part #	Price	Pg.
M71-1000-483-BK-KT	\$126.07	114
M71-1000-483-BK-KT	\$126.07	114
M71-1000-483-BL-KT	\$126.07	114
M71-1000-483-BL-KT	\$126.07	114
M71-1000-483-BL-KT	\$126.07	114
M71-1000-483-BL-KT	\$126.07	114
M71-1000-483-GN-KT	\$126.07	114
M71-1000-483-GN-KT	\$126.07	114
M71-1000-483-OR-KT	\$126.07	114
M71-1000-483-OR-KT	\$126.07	114
M71-1000-483-RD-KT	\$126.07	114
M71-1000-483-RD-KT	\$126.07	114
M71-1000-483-RD-KT	\$126.07	114
M71-1000-483-WT-KT	\$126.07	114
M71-1000-483-WT-KT	\$126.07	114
M71-1000-483-YL-KT	\$126.07	114
M71-1000-483-YL-KT	\$126.07	114
M71-2000-483-BK-KT	\$189.21	114
M71-2000-483-BK-KT	\$189.21	114
M71-2000-483-BL-KT	\$189.21	114
M71-2000-483-BL-KT	\$189.21	114
M71-2000-483-GN-KT	\$189.21	114
M71-2000-483-GN-KT	\$189.21	114
M71-2000-483-OR-KT	\$189.21	114
M71-2000-483-OR-KT	\$189.21	114
M71-2000-483-RD-KT	\$189.21	114
M71-2000-483-RD-KT	\$189.21	114
M71-2000-483-WT-KT	\$189.21	114
M71-2000-483-WT-KT	\$189.21	114
M71-2000-483-YL-KT	\$189.21	114
M71-2000-483-YL-KT	\$189.21	114
M71-2000-483-YL-KT	\$189.21	114
M71-AC-BC	\$59.00	104
M71-ADAPT	\$19.50	104
M71-BATT	\$85.00	104
M71-CABLE	\$16.95	104
M71-CLEAN	\$15.00	104
M71-HC	\$75.00	104
M71-QC	\$115.00	104
M71-R4300	\$56.34	115
M71-R4300	\$56.34	115
M71-R4400-WT	\$66.59	115
M71-R4400-WT	\$66.59	115
M71-R6000	\$56.34	115
M71-R6000	\$56.34	115
M71-R6200	\$56.34	115
M71-R6200	\$56.34	115
M71-R6400	\$61.97	115
M71-R6400	\$61.97	115
M71-R6600	\$73.34	115
M71-R6600	\$73.34	115
M71-R6600	\$73.34	115
M71-R6800-WT	\$73.34	115
M71-R6800-WT	\$73.34	115
M71-R6900-BL	\$66.59	115
M71-R6900-BL	\$66.59	115
M71-R6900-GN	\$66.59	115
M71-R6900-GN	\$66.59	115
M71-R6900-MA	\$66.59	115
M71-R6900-MA	\$66.59	115
M71-R6900-RD	\$66.59	115
M71-R6900-RD	\$66.59	115
M71-R6900-YL	\$66.59	115
M71-R6900-YL	\$66.59	115
M71-SC	\$45.00	104
M71C-230-412	\$48.54	112
M71C-240-498	\$42.39	109
M71C-318-498	\$43.56	109
M71C-375-412	\$51.16	112
M71C-375-422	\$58.80	112
M71C-375-430	\$54.57	107
M71C-375-498	\$44.24	109
M71C-475-412	\$53.91	112
M71C-475-422	\$67.63	112
M71C-500-412	\$53.91	112
M71C-500-422	\$58.80	112
M71C-500-423	\$49.55	108
M71C-500-428	\$62.48	106
M71C-500-430	\$54.57	107
M71C-500-483	\$61.58	107
M71C-500-498	\$31.72	109

Part #	Price	Pg.
M71C-500-499	\$31.72	109
M71C-500-530	\$57.27	113
M71C-500-581-WT	\$50.36	114
M71C-500-581-WT	\$50.36	114
M71C-500-581-YL	\$50.36	114
M71C-500-581-YL	\$50.36	114
M71C-500-581-YL	\$50.36	114
M71C-500-581-YL	\$50.36	114
M71C-500-581-YL	\$50.36	114
M71C-500-595-BL	\$47.22	105
M71C-500-595-BR	\$47.22	105
M71C-500-595-CL	\$47.22	105
M71C-500-595-GD	\$47.22	105
M71C-500-595-GN	\$47.22	105
M71C-500-595-GY	\$47.22	105
M71C-500-595-LB	\$47.22	105
M71C-500-595-OC	\$47.22	105
M71C-500-595-OR	\$47.22	105
M71C-500-595-PK	\$47.22	105
M71C-500-595-PL	\$47.22	105
M71C-500-595-RD	\$47.22	105
M71C-500-595-SB	\$47.22	105
M71C-500-595-TN	\$47.22	105
M71C-500-595-WT	\$47.22	105
M71C-500-595-YL	\$47.22	105
M71C-625-412	\$65.29	112
M71C-625-422	\$81.92	112
M71C-785-412	\$74.58	112
M71C-1000-422	\$81.28	112
M71C-1000-430	\$75.31	107
M71C-1000-483	\$85.22	107
M71C-1000-498	\$44.25	109
M71C-1000-499	\$44.25	109
M71C-1000-529	\$51.79	106
M71C-1000-530	\$75.91	113
M71C-1000-581-WT	\$70.52	114
M71C-1000-581-YL	\$70.52	114
M71C-1000-595-BK	\$65.87	105
M71C-1000-595-BL	\$65.87	105
M71C-1000-595-BR	\$65.87	105
M71C-1000-595-CL	\$65.87	105
M71C-1000-595-GD	\$65.87	105
M71C-1000-595-GN	\$65.87	105
M71C-1000-595-GY	\$65.87	105
M71C-1000-595-LB	\$65.87	105
M71C-1000-595-OC	\$65.87	105
M71C-1000-595-OR	\$65.87	105
M71C-1000-595-PK	\$65.87	105
M71C-1000-595-PL	\$65.87	105
M71C-1000-595-RD	\$65.87	105
M71C-1000-595-SB	\$65.87	105
M71C-1000-595-TN	\$65.87	105
M71C-1000-595-WT	\$65.87	105
M71C-1000-595-YL	\$65.87	105
M71C-1900-422	\$121.83	112
M71C-1900-430	\$112.71	107
M71C-1900-483	\$126.97	107
M71C-1900-498	\$66.40	109
M71C-1900-499	\$66.40	109
M71C-2000-529	\$71.97	106
M71C-2000-530	\$113.19	113
M71C-2000-581-WT	\$106.53	114
M71C-2000-581-YL	\$106.53	114
M71C-2000-595-BK	\$98.85	105
M71C-2000-595-BL	\$98.85	105
M71C-2000-595-BR	\$98.85	105
M71C-2000-595-CL	\$98.85	105
M71C-2000-595-GD	\$98.85	105
M71C-2000-595-GN	\$98.85	105
M71C-2000-595-GY	\$98.85	105
M71C-2000-595-L		

Part Number Index

www.BradyID.com

Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.	Part #	Price	Pg.
M71C-2000-595-YL	\$98.85	105	ODN08	\$135.78	168	PTL-8-422	\$58.52	118	PTLEP-173-593-SL	\$81.35	119
M71EP-167-593	\$94.45	106	OIL124	\$84.06	167	PTL-8-430	\$54.57	118	PTLEP-173-593-YL	\$81.35	119
M71EP-167-593-BK	\$94.45	106	OIL1818	\$103.56	167	PTL-9-423	\$42.74	118	PTLEP-174-593	\$81.35	119
M71EP-167-593-GN	\$94.45	106	OIL412	\$84.06	167	PTL-10-423	\$44.05	118	PTLEP-174-593-BK	\$81.35	119
M71EP-167-593-RD	\$94.45	106	OIL430	\$163.18	167	PTL-10-498	\$51.28	117	PTLEP-174-593-GN	\$81.35	119
M71EP-167-593-YL	\$94.45	106	OIL806	\$84.06	167	PTL-11-498	\$44.76	117	PTLEP-174-593-RD	\$81.35	119
M71EP-168-593	\$104.95	106	OIL99	\$119.48	167	PTL-13-423	\$46.95	118	PTLEP-174-593-SL	\$81.35	119
M71EP-168-593-BK	\$104.95	106	OP15	\$116.64	165	PTL-15-423	\$51.27	118	PTLEP-174-593-YL	\$81.35	119
M71EP-168-593-GN	\$104.95	106	OP15-DP	\$126.39	165	PTL-16-423	\$42.20	118	PTLEP-176-593	\$64.21	119
M71EP-168-593-RD	\$104.95	106	OP15-DPS	\$65.05	165	PTL-16-498	\$53.78	117	PTLEP-176-593-BK	\$64.21	119
M71EP-168-593-YL	\$104.95	106	OP15P	\$123.07	165	PTL-16-499	\$54.96	117	PTLEP-176-593-GN	\$64.21	119
M71EP-169-593	\$111.25	106	OP30	\$180.95	165	PTL-17-423	\$42.20	118	PTLEP-176-593-RD	\$64.21	119
M71EP-169-593-BK	\$111.25	106	OP30P	\$187.49	165	PTL-17-498	\$56.52	117	PTLEP-176-593-YL	\$64.21	119
M71EP-169-593-GN	\$111.25	106	OP50	\$160.09	165	PTL-18-498	\$37.03	117	PTLTB-498-240	\$42.39	118
M71EP-169-593-RD	\$111.25	106	OP100	\$98.01	165	PTL-18-499	\$37.82	117	PTLTB-498-318	\$43.56	118
M71EP-169-593-YL	\$111.25	106	OP100X-B	\$98.01	165	PTL-19-423	\$29.85	118	PTLTB-498-375	\$44.24	118
M71EP-171-593	\$104.95	106	OP100X-B	\$98.01	165	PTL-19-427	\$35.73	117	PVC18	\$210.82	169
M71EP-171-593-BK	\$104.95	106	OP150DND	\$142.81	165	PTL-19-498	\$40.18	117	PVC18	\$210.82	169
M71EP-171-593-GN	\$104.95	106	OP300	\$84.55	165	PTL-19-499	\$41.09	117	PVC24	\$305.49	169
M71EP-171-593-RD	\$104.95	106	OP315P	\$87.51	165	PTL-20-423	\$23.79	118	PVC24	\$305.49	169
M71EP-171-593-SL	\$104.95	106	OP550	\$44.06	165	PTL-21-427	\$27.36	117	PVC36	\$527.54	169
M71EP-171-593-YL	\$104.95	106	104600	\$60.41	220	PTL-21-498	\$32.84	117	PVC36	\$527.54	169
M71EP-173-593	\$79.75	106	104601	\$68.82	220	PTL-23-427	\$32.58	117	PVC42	\$609.01	169
M71EP-173-593-BK	\$79.75	106	104602	\$60.41	220	PTL-23-498	\$39.26	117	PWC-PK-1	\$30.86	83
M71EP-173-593-GN	\$79.75	106	104603	\$68.82	220	PTL-26-423	\$34.57	118	PWC-PK-3	\$30.86	83
M71EP-173-593-RD	\$79.75	106	PCCABLE-1	\$18.87	120	PTL-28-423	\$61.53	118	PWC-PK-36	\$30.86	83
M71EP-173-593-SL	\$79.75	106	PCK-4	\$27.56	120	PTL-28-498	\$52.21	117	PWC-PK-6	\$30.86	83
M71EP-173-593-YL	\$79.75	106	PD205A	\$33.15	103	PTL-28-499	\$53.52	117	PWM-PK-1	\$24.61	83
M71EP-174-593	\$79.75	106	PD206A	\$46.69	103	PTL-29-423	\$47.19	118	PWM-PK-2	\$24.61	83
M71EP-174-593-BK	\$79.75	106	PD240E	\$87.53	102	PTL-29-427	\$48.67	117	PWM-PK-3	\$24.61	83
M71EP-174-593-GN	\$79.75	106	PD241E	\$121.14	102	PTL-29-498	\$49.98	117	PWM-PK-8	\$24.61	83
M71EP-174-593-RD	\$79.75	106	PD265E	\$121.71	103	PTL-29-499	\$51.02	117	PWM-LC-3	\$24.61	83
M71EP-174-593-SL	\$79.75	106	PD322E	\$94.25	103	PTL-30-427	\$36.25	117	RAG24150	\$92.38	166
M71EP-174-593-YL	\$79.75	106	PD325E	\$94.72	102	PTL-30-498	\$43.97	117	R4310	\$29.02	117
M71EP-176-593	\$62.95	106	PD439G	\$89.24	103	PTL-30-499	\$45.16	117	R4410-BL	\$34.30	119
M71EP-176-593-BK	\$62.95	106	PD524E	\$94.72	102	PTL-31-427	\$45.80	117	R4410-RD	\$33.30	119
M71EP-176-593-GN	\$62.95	106	PD674E	\$155.33	63	PTL-31-498	\$51.02	117	R4410-WT	\$33.30	119
M71EP-176-593-RD	\$62.95	106	PD701E	\$127.19	103	PTL-31-499	\$52.34	117	R5300	\$13.68	126
M71EP-176-593-YL	\$62.95	106	PD995E	\$62.92	103	PTL-32-427	\$47.36	117	R6010	\$29.02	117
MC111E	\$104.09	59	PD997E	\$82.53	103	PTL-33-427	\$44.09	117	R6210	\$29.02	117
MIC-MTHSTD04	\$68.36	73	105370	\$145.46	196	PTL-34-427	\$36.51	117	R7300	\$13.68	126
MIC-MTIGPI G	\$81.38	73	105371	\$145.46	196	PTL-34-498	\$43.84	117	RAG1818	\$75.38	166
MIC-MTIGPI R	\$81.38	73	PLO23	\$16.10	219	PTL-37-423	\$34.57	118	RAG36150	\$138.50	166
MIC-MTIGPI Y	\$81.38	73	PLO23-BI	\$16.10	219	PTL-37-483-DANGER	\$48.07	119	RF100	\$81.45	163
MRO100	\$110.59	164	PLO27E	\$19.02	219	PTL-37-483-WARNING	\$48.07	119	RF300	\$68.85	163
MRO100-2	\$59.13	164	PLUG2	\$123.18	169	PTL-38-423	\$41.29	118	RF500	\$54.30	163
MRO15	\$126.39	164	PLUG2	\$123.18	169	PTL-38-483-DANGER	\$57.76	119	RFDP300	\$83.39	163
MRO150DND	\$155.89	164	PLUG3	\$149.60	169	PTL-38-483-WARNING	\$57.76	119	RFDP328DP	\$145.46	163
MRO15-DP	\$136.02	164	PLUG3	\$149.60	169	PTL-46-422	\$58.52	118	RFGRANULAR	\$620.75	168
MRO15-DPS	\$68.14	164	PLUG4	\$166.63	169	PTL-46-430	\$54.57	118	RFGRANULAR	\$620.75	168
MRO15P	\$132.69	164	PLUG4	\$166.63	169	PTL-64-427	\$16.75	117	RF0412	\$61.96	163
MRO24-DP	\$168.97	164	PLUG6	\$182.43	169	PTLEP-167-593	\$96.34	119	RF0510	\$105.67	168
MRO30	\$197.12	164	PLUG6	\$182.43	169	PTLEP-167-593-BK	\$96.34	119	RF0810	\$135.62	168
MRO30-DP	\$206.87	164	PS125E	\$25.64	52	PTLEP-167-593-GN	\$96.34	119	RFODP100	\$74.18	163
MRO30P	\$203.79	164	PS125S	\$25.64	52	PTLEP-167-593-RD	\$96.34	119	RFOP14P	\$62.84	163
MRO100-B	\$110.59	164	PS127E	\$25.64	53	PTLEP-167-593-YL	\$96.34	119	RFOP28DP	\$115.20	163
MRO300	\$87.51	164	PS128E	\$25.64	52	PTLEP-168-593	\$107.05	119	RFP100	\$87.27	163
MRO315P	\$90.47	164	PSPT-094-1-WT	\$45.67	118	PTLEP-168-593-BK	\$107.05	119	RFP14P	\$91.15	163
MRO350-DP	\$144.66	164	PSPT-125-1-WT	\$48.41	118	PTLEP-168-593-GN	\$107.05	119	RFP28-DP	\$151.27	163
MRO50	\$179.34	164	PSPT-125-175-WT	\$65.03	118	PTLEP-168-593-RD	\$107.05	119	RFP300	\$73.69	163
MPPE	\$67.33	102	PSPT-187-1-WT	\$53.91	118	PTLEP-168-593-YL	\$107.05	119	RFP314P	\$69.82	163
MS-50	\$116.77	163	PSPT-187-175-WT	\$72.22	118	PTLEP-169-593	\$113.48	119	RFP328-DP	\$120.24	163
MS-412	\$57.22	163	PSPT-250-1-WT	\$65.30	118	PTLEP-169-593-BK	\$113.48	119	RFP500	\$60.12	163
MS-806	\$57.22	163	PSPT-250-175-WT	\$87.93	118	PTLEP-169-593-GN	\$113.48	119	RK018A	\$86.96	58
MSSP	\$23.70	52	PSPT-375-1-WT	\$96.19	118	PTLEP-169-593-RD	\$113.48	119	RK085A	\$62.66	58
MUL-EITL535	\$162.75	73	PSPT-375-175-WT	\$129.40	118	PTLEP-169-593-YL	\$113.48	119	RK623E	\$304.61	58
MUL-EITL 230	\$162.75	73	PSPT-500-1-WT	\$111.21	118	PTLEP-171-593	\$107.05	119	SB-1010	\$3,160.00	169
MUL-EITHUSA01	\$68.36	73	PSPT-500-175-WT	\$149.54	118	PTLEP-171-593-BK	\$107.05	119	SB-1212	\$4,551.11	169
MUL-EITHUSA01A	\$95.70	73	PSPT-1000-1-WT	\$76.82	118	PTLEP-171-593-GN	\$107.05	119	SB-SL44	\$406.67	169
MVSD	\$72.71	102	PSPT-1000-175-WT	\$104.04	118	PTLEP-171-593-RD	\$107.05	119	SB-SL46	\$611.11	169
MVSDL	\$76.41	102	PTL-5-423	\$38.52	118	PTLEP-171-593-SL	\$107.05	119	SC-3000	\$382.64	169
MX01000	\$49.37	165	PTL-6-423	\$40.51	118	PTLEP-171-593-YL	\$107.05	119	SCAF2-STHUSA	\$101.68	73
MXP-C20	\$133.22	166	PTL-7-422	\$42.20	118	PTLEP-173-593	\$81.35	119	SCAF2-STHUSAA	\$153.80	73
MXP-020	\$122.11	166	PTL-7-423	\$35.64	118	PTLEP-173-593-BK	\$81.35	119	SCAF-STH132	\$68.36	73
MXP-U20	\$122.11	166	PTL-7-430	\$39.50	118	PTLEP-173-593-GN	\$81.35	119	SCAF-STH132A	\$119.63	73
MXU1000	\$59.24	164	PTL-7-498	\$49.20	117	PTLEP-173-593-RD	\$81.35	119	SCAF-STH146	\$68.36	73

Part Number Index

www.BradyID.com

Part #	Price	Pg.
SCAF-STSI593	\$162.75	73
SCAF-STSI594	\$162.75	73
SCAF-STSI751	\$183.75	73
SC-DP2	\$335.36	169
SC-DP4	\$500.00	169
SC-DPR	\$522.22	169
SC-SD2	\$215.56	169
SD02M	\$13.46	223
SF647E	\$28.71	225
SH1824	\$56.21	52
SIR36	\$379.93	166
SIR36150	\$214.58	166
SIR72	\$379.93	166
SKA-20	\$294.88	170
SKA-55	\$573.25	171
SKA-95	\$1,032.73	171
SKA-ATK	\$381.03	170
SKA-BKT	\$84.43	170
SKA-K2	\$694.80	171
SKA-LT	\$1,824.31	171
SKA-PP	\$55.30	170
SKA-SAK	\$166.63	170
SKA-XLT	\$2,332.85	171
SKH-20	\$354.50	170
SKH-55	\$592.72	171
SKH-95	\$1,121.99	171
SKH-ATK	\$400.90	170
SKH-BKT	\$88.13	170
SKH-K2	\$753.54	171
SKH-LT	\$1,984.78	171
SKH-PP	\$61.84	170
SKH-SAK	\$181.69	170
SKH-XLT	\$2,527.87	171
SKO-20	\$294.88	170
SKO-55	\$573.22	171
SKO-95	\$1,032.75	171
SKO-ATK	\$355.61	170
SKO-BKT	\$84.43	170
SKO-K2	\$678.14	171
SKO-LT	\$1,824.31	171
SKO-PP	\$55.79	170
SKO-SAK	\$166.63	170
SKO-XLT	\$2,332.85	171
SKR-20	\$280.84	170
SKR-95	\$983.56	171
SKR-ATK	\$362.89	170
SKR-PP	\$52.67	170
SM681A	\$76.14	59
SM682A	\$137.08	59
SP184L	\$18.70	37
SP818V	\$23.69	37
SPC10	\$153.18	168
SPC50	\$219.71	165
SPC100	\$94.92	165
SPC150	\$203.66	165
SPC152	\$214.15	165
SPC200	\$106.76	165
SPC300	\$79.99	165
SPC318	\$96.40	168
SPC500	\$60.11	165
SPC510	\$149.84	168
SPC518	\$102.81	168
SPC810	\$282.90	168
SPC1900	\$149.84	168
SPC5510	\$295.61	168
SR50	\$129.77	165
SR100	\$81.66	165
SR1825	\$36.54	165
SR1850	\$37.52	165
SR3600	\$173.17	165
SR3625	\$82.33	165
SW46	\$103.93	167
SXT100	\$88.50	165
SXT15P	\$93.56	165
SXT200	\$103.56	165
SXT30DP	\$145.03	165

Part #	Price	Pg.
SXT300	\$35.00	165
T218	\$7.53	208
T220	\$7.97	208
TC8	\$52.82	197
TH2	\$14.10	197
TLS2200	\$795.00	117
TLS2200-AC	\$123.83	117
TLSHM-QUICKCH	\$121.26	117
TM58	\$467.44	166
UN1019	\$237.61	166
UN1113	\$158.36	166
UN1719	\$162.19	166
UN3800	\$237.61	166
UXT100	\$102.82	164
UXT15P	\$107.63	164
UXT200	\$110.59	164
UXT300	\$102.82	164
UXT30DP	\$191.69	164
V1AE01A	\$14.95	38
V1EW03A	\$14.95	38
V1FA03A	\$14.95	38
V1FE15A	\$14.95	37
V1FEG1G	\$23.70	37
V1FL15A	\$14.95	37
V1SWG4G	\$23.70	34
V1SWG4G	\$23.70	34
V2SS24A	\$18.69	41
WSLO	\$8.14	220
105368	\$145.46	196
105369	\$145.46	196
WM-0-PK	\$43.20	83
WM-1-PK	\$43.20	83
WM-2-PK	\$43.20	83
WM-3-PK	\$43.20	83
WM-4-PK	\$43.20	83
WM-5-PK	\$43.20	83
WM-6-PK	\$43.20	83
WM-7-PK	\$43.20	83
WM-8-PK	\$43.20	83
WM-9-PK	\$43.20	83
WM-1-33-PK	\$43.20	83
WM-34-66-PK	\$43.20	83
WM-67-99-PK	\$43.20	83
WM-100-124-PK	\$43.20	83
WM-125-149-PK	\$43.20	83
WM-A-Z-PK	\$43.20	83
WML-205-292-1	\$33.95	126
WML-205-292-2S	\$49.34	126
WML-205-292-75	\$28.51	126
WML-211-292-1	\$41.81	126
WML-211-292-75	\$37.71	126
WML-305-292	\$33.76	126
WML-305-292-2S	\$56.57	126
WML-305-499	\$59.84	126
WML-305-502	\$58.59	126
WML-311-292	\$45.42	126
WML-317-292	\$53.60	126
WML-505-499	\$37.80	126
WML-505-499-2S	\$54.67	127
WML-505-502	\$37.00	126
WML-505-502-2S	\$53.69	127
WML-511-292	\$32.13	127
WML-511-499	\$45.15	126
WML-511-502	\$44.26	126
WML-517-292	\$39.83	127
WML-705-499	\$40.63	126
WML-705-502	\$39.84	126
WML-711-292	\$38.04	127
WML-711-499	\$48.66	126
WML-711-502	\$48.13	126
WML-717-292	\$51.65	127
WML-905-502	\$43.23	126
WML-911-499	\$52.68	126
WML-911-502	\$51.34	126
WMS-111-321	\$272.85	127
X-7-422	\$39.92	122

Part #	Price	Pg.
X-7-498	\$42.10	121
X-11-498	\$42.18	121
X-11-499	\$33.22	122
X-17-422	\$53.34	123
X-17-428-SV-BK	\$62.55	122
X-17-483	\$56.84	122
X-18-498	\$43.37	121
X-19-422	\$45.07	122
X-19-498	\$37.14	121
X-20-428-SV-BK	\$40.02	122
X-20-483	\$36.05	122
X-21-498	\$36.96	121
X-23-498	\$39.09	121
X-24-428-SV-BK	\$55.05	122
X-29-422	\$59.15	123
X-29-428-SV-BK	\$71.32	122
X-30-422	\$55.40	122
X-30-428-SV-BK	\$55.94	122
X-31-498	\$43.67	121
X-61-483	\$28.33	122
X-82-499	\$38.21	122
X-83-499	\$38.21	122
X-84-499	\$34.40	122
X-103-498	\$37.96	121
X-130-499	\$36.77	122
X-132-422	\$60.82	122
X-162-498	\$38.06	121
X-162-499	\$36.93	122
X-163-498	\$41.42	121
XC-240-498	\$52.31	122
XC-318-498	\$53.59	122
XC-375-422	\$55.40	123
XC-375-498	\$54.87	122
XC-375-499	\$54.87	122
XC-475-422	\$52.26	123
XC-500-499	\$57.06	120
XC-500-595-BL-WT	\$45.07	120
XC-500-595-CL-BK	\$37.56	120
XC-500-595-GN-WT	\$45.07	120
XC-500-595-OR-BK	\$45.07	120
XC-500-595-RD-WT	\$45.07	120
XC-500-595-WT-BK	\$45.07	120
XC-500-595-WT-RD	\$45.07	120
XC-500-595-YL-BK	\$45.07	120
XC-750-499	\$59.33	120
XC-750-595-BL-WT	\$55.06	120
XC-750-595-CL-BK	\$45.90	120
XC-750-595-GN-WT	\$55.06	120
XC-750-595-OR-BK	\$55.06	120
XC-750-595-RD-WT	\$55.06	120
XC-750-595-WT-BK	\$55.06	120
XC-750-595-WT-RD	\$55.06	120
XC-750-595-YL-BK	\$55.06	120
XC-1000-422	\$64.43	123
XC-1000-499	\$61.18	120
XC-1000-595-BL-WT	\$56.70	120
XC-1000-595-CL-BK	\$47.26	120
XC-1000-595-GN-WT	\$56.70	120
XC-1000-595-OR-BK	\$56.70	120
XC-1000-595-RD-WT	\$56.70	120
XC-1000-595-WT-BK	\$56.70	120
XC-1000-595-WT-RD	\$56.70	120
XC-1000-595-YL-BK	\$56.70	120
XC-1500-595-BL-WT	\$67.02	120
XC-1500-595-CL-BK	\$55.85	120
XC-1500-595-GN-WT	\$67.02	120
XC-1500-595-OR-BK	\$67.02	120
XC-1500-595-RD-WT	\$67.02	120
XC-1500-595-WT-BK	\$67.02	120
XC-1500-595-WT-RD	\$67.02	120
XC-1500-595-YL-BK	\$67.02	120
XPERT-ABC	\$399.95	120
XPERT-ABC-KIT-LM	\$641.00	120
XPERT-ABC-KIT-VD	\$567.00	120
XPERT-AC	\$42.00	120
XPERT-CONT	\$250.00	120

Part #	Price	Pg.
XPERT-HC-ABC	\$75.00	120
XPERT-HC-KEY	\$75.00	120
XPERT-KEY	\$399.95	120
XPS-125-1	\$51.28	121
XPS-125-CONT	\$44.50	121
XPS-125-CONT-YL-BK	\$44.50	121
XPS-187-1	\$56.29	121
XPS-187-CONT	\$48.87	121
XPS-187-CONT-YL-BK	\$48.87	121
XPS-250-1	\$67.57	121
XPS-250-CONT	\$53.79	121
XPS-250-CONT-YL-BK	\$53.79	121
XPS-375-1	\$97.62	121
XPS-375-CONT	\$78.84	121
XSL-11-427	\$48.71	121
XSL-17-427	\$56.84	121
XSL-18-427	\$39.92	121
XSL-19-427	\$45.07	121
XSL-21-427	\$36.05	121
XSL-21-427-YL-BK	\$39.92	121
XSL-23-427	\$46.37	121
XSL-23-427-YL-BK	\$50.23	121
XSL-29-427	\$57.98	121
XSL-30-427	\$43.80	121
XSL-31-427	\$54.12	121
XSL-31-427-YL-BK	\$59.28	121
XSL-32-427	\$60.55	121
XSL-33-427	\$57.98	121
XSL-34-427	\$46.37	121
XSL-96-427	\$34.76	121
XSL-102-427	\$32.18	121
XSL-103-427	\$51.54	121
XSL-115-427	\$46.37	121
XSL-116-427	\$36.05	121

Product Index

www.BradyID.com

Product	Pg.
A	
5S Marking Supply Kits	85
AC Sensor	217
Accident Prevention Tags	71
Admittance Signs	24
Aisle Marking Tapes	89
Alert Signs	25
Aluminum Utility Panels	66
ANSI Z535 Safety Signs	26
Anti-Skid Floor Tape	95
Arc Flash Labels	68
Arc Flash Training Aids	69
Arrows - Vinyl	96
Arrows - ToughStripe	89
Asbestos Labels	64
ASME Standard For Pipe Identification	76
B	
Barricade Tape	97
Battery Cleaning & Charging Safety Kit	60
BBP31 Label Printer	132-141
Bilingual Signs	27
Binder Holders	58
Biohazard, Chemical & Hazardous Material Signs	28
Blank Aluminum Valve Tags	74
Blank Brass Valve Tags	74
Blank High Performance Wrap-Around Pipe Marker	79
Blank HPHV Carrier	154
Blank NFPA Placards	62
Blank Signs	26
Blank Stainless Steel Tags	74
Bloodborne Pathogen Compliance Center	60
BLS1255 Laminator	158
BLS850 Laminator	159
BMP21 Label Printer	116
BMP71 Label Printer	104-115
Border Marking Tape	85
Bouffant Cap / Beard	102
Bradycone Warning System	98
BradyGlo Door Handle Markers	93
BradyGlo Exit & Directional Signs	34
BradyGlo Handrail Covers	93
BradyGlo Stair-Nosing	93
BradyLink Warning Chain and Links	98
BradyLink Warning Posts	98
BradyLite Reflective Numbers & Letters	67
BradySnap-On & Strap-On Pipe Markers	79
Bradystake Anchors	96
Bradystake Warning Stake Labels	96
Braille (ADA) Signs	26
Brass Valve Tags	74
C	
Cabinet Label	70
Cable & Chain Lockouts	210
Cable Lock Seals	100
Center Marks	89
Chain	75
Chemical & Hazardous Materials Signs	28
Circuit Breaker Lockouts	214

Product	Pg.
Clear Acrylic Dispenser Tray	103
Compact Ear Plug Dispenser	103
Confined Space Signs	30
Container Labels	61
Corner Marks - Vinyl	85
Corner Marks - ToughStripe	89
Custom Pipe Marker Request	82
Custom Signs	55
D	
Deluxe Glove Dispenser	102
Deluxe Visitor Spec	102
Detectable Identoline Warning Tape	99
Directional Flow Arrow Tape	81
Dispensers	102
Display Board Accessories	86
Divided Hearing Protection Dispenser	103
Divider Marks - ToughStripe	89
Door Signs	30
Dots - Vinyl	96
Dots - ToughStripe	89
Double Bottle Eye Wash Station	103
Durable Plastic Tags	74
Dust Mask Dispenser	102
E	
E-Z Check Plus GFI Circuit Tester	60
Ear Plug Dispenser	103
Ear Protection Signs	44
Egress Signs	32
Electrical Hazard Signs	31
Electrical Lockouts	219
Electrical Tools & Testers	221
Emergency Evacuation Frames	32
Emergency Lighting	32
Energy Source Labels & Tags	224
EntryTag	73
Envelopes	228
Eye Protection Signs	44
F	
Facility Safety Signage Assessment	232
Fire Safety Signs	36
First Aid Signs	38
Floor Marking Tape	89
Floor Signs	39
Floor Stands	99
Footprints - Vinyl	95
Footprints - ToughStripe	89
Forklift Tag	73
Funny Signs	40
G	
Gas & Air Line Lockout	222
Gate Signs	40
Gauge Marking Labels	70
GHS Standards	63
GlobalMark 2 Industrial Label Maker	142
Glove Dispensers	102
Glow-in-the-Dark Arrow Tape	93
Glow-in-the-Dark Floor Tapes	93

Product	Pg.
Gothic Quick-Align Kits	67
Graphic Pro Accessories	154
Group Lockout Boxes	205
Group Lockout Hasps	208
H	
Handicapped Signs	40
HandiMark Label Maker Materials	124
Handy Cone Floor Signs	98
Hard Hat Emblems	70
Hasps	208
Hazard Marking Diecut Cleats	95
Hazardous Information Placards	62
Hazardous Material Shipping Labels	65
Hazardous Waste Labels	64
Head Wear Dispensers	102
Heavy Duty Anti-Skid Tapes	95
Heavy Duty Floor Stands	99
High Intensity Stop Sign	50
High Performance Pipe Markers	80
High Visibility Signs	37
HMIG Labels Station	62
HMIG Self-Laminating Labels	62
Hospital Directional Signs	40
I	
I.D. Pro Plus Printer	126
Identoline Underground Warning Tape	99
IDXPRT Handheld Labeler	120
Indoor Numbers & Letters	66
Indoor Numbers & Letters Combo Packs	66
Indoor/Outdoor Numbers & Letters	67
Information Centers	59
Inspection & Material Control Tags	71
InspectNTrack Software	157
J	
Job Site Center	59
L	
Labelizer Plus & VersaPrinter Tapes	152
LabelMark Labeling Software	156
LadderTags	73
Laminators	158
Large Capacity Ear Plug	103
Large Capacity Eye Protection Dispenser	103
Lead Seals	75
Lean Communication Boards	86
Lean Machines Book	87
Lean Products	84
Load Center & Residential Wire Markers	83
Lockout For Life DVD	227
Lockout Kits	180
Lockout PRO Visual Procedure Writing Software	229
Lockout Procedure Station	228
Lockout Safety Training Booklet	54
Lockout Stations	188
Lockout Tags	194
Lockout/Tagout	178
Lockout/Tagout Barricades	225

Product	Pg.
Lockout/Tagout eLearning Courses	227
Lockout/Tagout Floor Stands	225
Lockout/Tagout for Authorized & Affected Personnel	227
Lockout/Tagout Handbook	226
Lockout/Tagout Hard Hat Labels	226
Lockout/Tagout Magnetic Signs	225
Lockout/Tagout Safety Labels	225
Lockout/Tagout Safety Poster	226
Lockout/Tagout Safety Signs	225
Lockout/Tagout Training Booklet	226
Lockout/Tagout Training: A Program for Employees	227
Lockout/Tagout Wallet Safety Cards	226
M	
Machine & Equipment Labels	70
Machine & Operational Signs	41
Magnetic Numbers	67
Maintenance Signs	42
Mark Aisles & Passageways	95
Marking Flags	99
MarkWare Facility Identification Software	156
MarkWare Lean Software	84
Metal Ball Seals	100
MicroTag	73
MiniMark Industrial Label Printer	128
Mr. Ouch Labels	68
MSDS Binders	59
MSDS Metal Cabinet	58
MSDS Training Binder Insert	59
MSDS/Job Site Safety Document Center	59
MultiTag	73
N	
NetDoc Network Documentation	157
NFPA Diamond Labels	62
NFPA Placard Kits	62
NFPA70 National Electric Code	68
No Smoking Signs	43
Numbers & Letters	66
O	
One Step SecurAlert Badges	101
OSHA Safety Poster	54
OSHA Standards	61
Outdoor Numbers & Letters Combo Packs	66
P	
Padlock Centers	202
Padlocks	198
PCB Markers	64
Pennant Barricade Tape	97
Perimeter L.E.D. Exit Signs	32
Personal Protective Wear (PPE) Signs	45
Pipe Banding Tape	81
Pipe Marker Material Selection	77
Pipe Markers	76
Plastic Poly-Lok	100
Porta-Pack Wire Marker Books	83
Posters & Banners	52

Product	Pg.
PowerMark Sign & Label Maker	148
PowerMark Tapes	150
PPE Dispenser	102
Pre-Spaced Floor Marking Shapes	89
Print-On-Demand ToughStripe	90
Production Status Tags	71
Pull-Tite Seals	100

Q

Quik-Apply Nylon Straps	75
-------------------------	----

R

Radiation & Laser Signs	45
Re-Pulpable Barricade Tape	97
Recycle & Environment Signs	46
Reflective Numbers & Letters	67
Reinforced Barricade Tape	97
Restroom Signs	46
Retractable Badge Holder	101
Reversible Floor Stands	99
Right To Know Compliance Centers	58
RTK Wallet Card	62

S

Safe-T-Grip Fuse Puller	60
Safety Banners	54
Safety Glasses Holder	103
Safety Information Centers	58
Safety Signs	24
Scaffolding Tags	72
Scoreboard Signs	46
Security Products	100
Security Signs	46
Self Sticking Vinyl Arrows	81
Self-Expiring Parking Permits	101
Self-Laminating Tags	72
Self-Sticking Vinyl Pipe Markers	78
Shadow Vinyl	85
Shoe Cover Dispenser	103
Sign Accessories	51
Sign Base	51
Sign Mounting Tape	51
Sign Posts	51
Sign/Permit Holder & Entry Permits	60
Signs	22-57
Admittance Signs	24
Alert Signs	25
ANSI Z535 Safety Signs	26
Bilingual Signs	27
Biohazard, Chemical & Hazardous Material Signs	28
Blank Signs	26
BradyGlo Exit & Directional Signs	34
Braille (ADA) Signs	26
Chemical & Hazardous Materials Signs	28
Confined Space Signs	30
Custom Signs	55
Door Signs	30
Ear Protection Signs	44
Egress Signs	32
Electrical Hazard Signs	31

Product	Pg.
Emergency Evacuation Frames	32
Emergency Lighting	32
Eye Protection Signs	44
Fire Safety Signs	36
First Aid Signs	38
Floor Signs	39
Funny Signs	40
Gate Signs	40
Handicapped Signs	40
High Intensity Stop Sign	50
High Visibility Signs	37
Hospital Directional Signs	40
Lockout Safety Training Booklet	54
Machine & Operational Signs	41
Maintenance Signs	42
No Smoking Signs	43
OSHA Safety Poster	54
Perimeter L.E.D. Exit Signs	32
Personal Protective Wear (PPE) Signs	45
Posters & Banners	52
Radiation & Laser Signs	45
Recycle & Environment Signs	46
Restroom Signs	46
Safety Banners	54
Safety Signs	24
Scoreboard Signs	46
Security Signs	46
Sign Accessories	51
Sign Base	51
Sign Mounting Tape	51
Sign Posts	51
Signs Materials Guide	23
Temporary Signs	47
Traffic Control Paddles	50
Traffic Control Signs	48
Traffic Signs	48
Training Posters & Banners	52
Tuff-N-Light U-Channel Posts	51
U-Channel Sign Posts	51
Vandal-Proof Tufnut	51
Signs Materials Guide	23
Simulated Surveillance Camera	100
Snap-On Cable Markers	81
Snap-On Pipe Markers	79
Software	156
Solid "S" Hooks	75
Solid Color Pipe Banding Tape	81
Sorbent Products	160-175
20 Gallon Lab Pack	170
55 Gallon Drum	170
6.5 Gallon Spill Bucket	170
95 Gallon Overpack	170
ALLWIK SOCs	166
Attack Pac	170
Barrier Spill Matting	166
Basic Oil Only Pads & Rolls	165
Basic Universal Pads & Rolls	164
Battlemat	164
Chemical Pads & Rolls	166
Cobra Coil SOCs	167
Dri-Zorb	168
Drum Top Covers	169
Economy Spill Kit	170
ENV Series	165

Product	Pg.
GP - General Purpose	164
HAZWIK SOCs	167
HT - High Traffic Series	164
Loose Granular	168
Marine	168
Mats & Rugs	166
MAXX Chemical	166
MAXX Packs	166
Mobile Spill Kaddie	171
Mobile Spill Truck - Large	171
Mobile Spill Truck - X Large	171
MRO Plus	164
Oil Drag Net	168
Oil Gator	168
Oil Only Pads & Rolls	165
Oil Only SOCs	167
Oil Plus	165
Pillows	167
Rag Rug	166
Re-Form Multiwick SOCs	167
Re-Form Oil Only Pads & Rolls	163
Re-Form Oil Only SOCs	167
Re-Form Pads & Rolls	163
Re-Form Plus Pads & Rolls	163
Re-Form X Plus Pads & Rolls	163
Slikstopper Drain Cover	169
SLIKWIK SOCs	167
SOCs	167
Sorbent Booms	168
Sorbent Center	169
Sorbent Industrial Rug	166
Sorbent Specifications Index	173
SPC Oil Only Series	165
Spill Berms	169
Spill Containment	169
Spill Pallets	169
Static Resistant Oil Only	165
Storm Drain Guards	167
SXT Oil Only	165
Trackmat Roll	166
Universal Pads & Rolls	164
Universal Plus Chemical	166
Universal SOCs	167
UXT - Xtra Tough	164
Stainless Wire	75
Standard Operating Procedures Center	59
Striped Warning & Check Tape	89
Striped Warning Posts	98
Striped Warning Posts & Chain	225
Stripes & Solid Reflective Tape	95
Suggestion Box	59
Tags	71
Temporary Signs	47
Tensabarrier Barricade System	97
The Brady Boys Barrier	98
TLS 2200 Thermal Label Printer	117
Tool Board & Workbench Marking Supplies	85
ToughStripe Floor Marking Tape	88
Traffic Control Paddles	50
Traffic Control Signs	48
Traffic Signs	48

Product	Pg.
Training Posters & Banners	52
Tuff-N-Light U-Channel Posts	51U
U-Channel Sign Posts	51
Universal Waste Labels	64

V

Valve Chart Frames	74
Valve Lockouts	212
Valve Tag Fastening Devices	75
Valve Tags	74
Vandal-Proof Tufnut	51
Vehicle Placards	65
Vinyl Cloth Wire Marker Cards	83
Visual Confined Space Procedure Service	233
Visual Lockout Procedure Service	230
Visual Systems Presentation CD-Rom	87
Visual Thinking Book	87
Visual Workplace	87
Visual Workplace eLearning Courses	86
Visual Workplace Foundations Training Kit	87
Visual Workplace Products	84
Voltage Labels	70

W

Warning Labels	68
Warning Message Tapes	95
Warning Strip Anti-Skid Tape	95
Waste Disposal Labels	64
Wire Markers	83
Woven Barricade Tape	97
Write-On Inspection Labels	70
Write-On Right-To-Know Labels	61
Write-On Self-Laminating	
Wire & Cable Markers	83

Z

Zinc Wire Clamps	75
------------------	----

CHECK OUT WHAT'S NEW AT:

NEW!



e-Learning Online Training Courses

Brady now offers online training courses on the topics of lockout/tagout and visual workplace. These interactive courses provide a thorough, comprehensive overview of the subject, with real-life application scenarios and quizzes to facilitate learning and remembering. They are available 24 hours a day online, so you can train at your own pace – without ever needing to leave your facility.

**Only available at:
www.BradyID.com/elearning**

Available Training Courses:

Lockout/Tagout:

- Lockout/Tagout for the Authorized Worker
- Lockout/Tagout for the Corporate Safety Leader

Visual Workplace:

- Introduction to Visual Workplace
- Visual 5S – Optimizing Workplace Organization
- Visual TPM – Enhancing Equipment Reliability and Maintenance Efficiency

Lockout/Tagout Training Courses

Catalog No.	Description	Price
142253	LOTO For Authorized Workers (approx. length 1hr 30min)	\$29.95
142254	LOTO For Corporate Safety Leader (approx. length 1hr)	\$29.95
142255	e-Learning Bundle: (1)LOTO For Auth Worker and (1) LOTO for Corp Safety Leader	\$49.95

Visual Workplace Training Courses

Catalog No.	Description	Price
142256	Introduction to Visual Workplace (approx. 30-40mins)	\$29.95
142257	Visual 5S: Optimizing Workplace Organization (approx. 30-40mins)	\$29.95
142258	Visual TPM: Enhancing Equip. Reliability & Maint. Efficiency (approx. 30-40mins)	\$29.95
142259	e-Learning Bundle: (1) Intro to VW, (1) Visual 5S and (1) Visual TPM	\$74.95

BradyID Quick Reference Guide

Lean / Visual Workplace	www.BradyID.com/visualworkplace
Lockout / Tagout	www.BradyID.com/lockouttagout
Slips / Trips / Falls	www.BradyID.com/slipstripsfalls
Voice / Data Communications	www.BradyID.com/datacomm
Safety Services	www.BradyID.com/idservices
SPC Sorbent Products	www.BradyID.com/spc

New Products Online

BMP®21 Label Printer	www.BradyID.com/bmp21
BMP®71 Label Printer	www.BradyID.com/bmp71
BBP®31 Sign & Label Printer	www.BradyID.com/bbp31
ToughStripe® Floor Marking Tape	www.BradyID.com/toughstripe
e-Learning Online Training	www.BradyID.com/elearning

Also find Brady on:



Online Custom Design Tool

Design products to help meet your safety and compliance needs.

NEW!

Brady's custom design tools are your online solution for creating unique signs, valve tags and property ID tags.

Choose the custom sign shop tool of your choice and in just a matter of minutes, you'll be creating a professional sign, tag or marker that your facility needs.

The made-to-order process lets you see the sign or tag as it's created, while you select the pictograms and text that make up your customized safety signs and tags.

Easy as 1, 2, 3!

- 1) Select your category
- 2) Customize your product
- 3) Add to your shopping cart


Create Custom Products In Minutes At BradyID.com



Traffic Signs



Safety Signs



Tags



Pipe Markers



Property ID Tag



Graphical
Lockout/Tagout
Procedures

Your custom products ship in 24-48 hours!

The NEW BradyID.com!

OVER 30,000 PRODUCTS NOW AT YOUR FINGERTIPS

- Product Info
- Product Demos
- Custom Orders
- Whitepapers
- Webinars
- And more!

Brady warrants only to the buyer that the products and parts set forth herein will be free from defects in material and workmanship from the date of purchase for a period of one year. Brady's sole obligation under the above warranty shall be to repair or replace the defective products or parts during the warranty period. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GIVEN, AND BRADY EXPRESSLY DISCLAIMS ALL OTHER WARRANTIES, INCLUDING AND WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. All statements, technical information, or recommendations relating to the products or parts are based upon tests believed to be reliable, but do not constitute a guaranty or warranty. BRADY SHALL NOT UNDER ANY CIRCUMSTANCES WHATSOEVER BE LIABLE TO ANY PARTY FOR LOSS OF PROFITS, DIMINUTION OF GOOD WILL, OR ANY OTHER SPECIAL, CONSEQUENTIAL, OR INCIDENTAL DAMAGES WHATSOEVER WITH RESPECT TO ANY CLAIM IN CONNECTION WITH BRADY PRODUCTS AND/OR PARTS. Brady's maximum liability for warranty claims is limited to the invoice price of the product or price claimed defective.

PRICES AND AVAILABILITY ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Also find Brady On:



USA

Customer Service: 1-888-272-3946

Inside Sales: 1-888-311-0775

www.BradyID.com

Canada

Customer Service: 1-800-263-6179

www.BradyCanada.ca

Mexico

Customer Service: 1-800-262-7777

Inside Sales: 1-800-262-7777 ext 177

www.BradyLatinAmerica.com

Priced



Y1632974 MS1632974

© 2011 Brady Worldwide, Inc. All Rights Reserved.

 **BRADY**[®]
WHEN PERFORMANCE MATTERS MOST™