




# PROGRESS

COMMERCIAL LIGHTING



Multi-Family  
Hospitality  
Assisted Living  
Extended Stay  
Live / Work Housing





145

# CONTENTS

Linear / Troffer . . . . .	3
Exit / Emergency . . . . .	9
Close-to-Ceiling . . . . .	15
Ceiling Fans . . . . .	33
Sconces . . . . .	37
Bath & Vanity . . . . .	43
Hanging . . . . .	49
Undercabinet . . . . .	61
Recessed . . . . .	65
Outdoor . . . . .	73
Area / Site . . . . .	89



# A COMPLETE SOLUTION FOR LIGHT COMMERCIAL PROJECTS

Our recently expanded offering includes light commercial and commercial luminaires that work together to provide a unique solutions approach to a variety of multi-use applications, including multi-family, hospitality, assisted living – and many others.

We invite you to browse among our collection of proven Progress Lighting products, which features more than 100 new LED options. LED technology provides numerous benefits over traditional lamp sources, such as energy savings, increased light and color output, easy installation and low maintenance features.

We understand that multi-use projects require lighting solutions that not only meet interior expectations, such as decorative fixtures for the bath and vanity, kitchen and living areas – but also exterior applications that consider security, pedestrian safety, maintenance and site lighting needs.

For more than 100 years, Progress Lighting has provided a diverse selection of fixtures that represent aesthetics, performance, innovation and value. We continue to deliver complete lighting packages that meet individual project needs.

Please visit our website at [progresscommercial.com](http://progresscommercial.com).







## Linear / Troffer

Adding general and task lighting to multi-purpose areas, including stairwells, laundry areas, common rooms, offices and more can be done beautifully and efficiently with low profile linear and troffer options. And because they feature LED and CFL sources, you'll enjoy energy cost savings.



## T8 Lensed Fluorescent Lay-in

Product No.	Lamp	Lens	Configuration	Size
<b>PCILT-32T8-222</b>	2 T8, 32w	A12	2 x 2	24" L., 4-1/2" H., 23-3/4" W.
<b>PCILT-32T8-242</b>	2 T8, 32w		2 x 4	48" L., 3-1/8" H., 24" W.
<b>PCILT-32T8-243</b>	3 T8, 32w		2 x 4	
<b>PCILT-32T8-142</b>	2 T8, 32w		1 x 4	48" L., 4-1/4" H., 11-3/4" W. (Lamps Lay-in) 12-3/4" W. (Lamps Flanged)



PCILT-32T8-222



PCILT-32T8-243



PCILT-32T8-142

## Lensed LED Lay-in

Product No.	Lamp	Lens	Configuration	Lumens	Size	Color Temperature
<b>PCILT-LED-22-30K</b>	LED 43w	A12	2 x 2	3775	24" L., 4-1/4" H., 24" W.	3000K
<b>PCILT-LED-22-35K</b>				3850		3500K
<b>PCILT-LED-24-30K</b>	LED 45w		2 x 4	4600	48" L., 3-1/8" H., 24" W.	3000K
<b>PCILT-LED-24-35K</b>				4800		3500K



PCILT-LED-22-35K



PCILT-LED-24-30K

## Recessed Indirect Lay-in

Product No.	Lamp	Configuration	Size
<b>PCIST-17T8-222</b>	2 T8, 17w	2 x 2	25" L., 5-1/4" H., 25" W.
<b>PCIST-32T8-242</b>	2 T8, 32w	2 x 4	48" L., 5-1/4" H., 25" W.



PCIST-17T8-222



PCIST-32T8-242

## Recessed Performance LED

Product No.	Lamp	Lumens	Configuration	Size	Color Temperature
<b>PCICT-LED-22-30K</b>	LED 35w	3500	2 x 2	24" L., 5-3/15" H., 24" W.	3000K
<b>PCICT-LED-22-35K</b>		3700			3500K
<b>PCICT-LED-24-30K</b>	LED 40w	4450	2 x 4	48" L., 5-3/15" H., 24" W.	3000K
<b>PCICT-LED-24-35K</b>		4800			3500K



PCICT-LED-22-30K



PCICT-LED-24-30K



## Flourescent Wrap

Product No.	Finish	Lamps	Size
<b>P7183-30EB</b>	White, Baked Enamel	2 17w T8	24" L., 3" H., 7-3/4" W.
<b>P7186-30EB</b>		2 32w T8	
<b>P7196-30EB</b>		4 32w T8	48" L., 3" H., 15" W.



## Low Profile LED Wraparound

Product No.	Lamp Type	Lumens	Size	Color Temperature
<b>PCILW-LED-2-30K</b>	LED 25w	2550	24" L., 2-13/16" H.,	3000K
<b>PCILW-LED-2-35K</b>		2600	8-5/16" W.	3500K
<b>PCILW-LED-4-30K</b>	LED 48w	4650	48" L., 2-13/16" H.,	3000K
<b>PCILW-LED-4-35K</b>		4800	8-5/16" W.	3500K



## Flourescent Wall Mount

Product No.	Lamp Type	Nom. Length	Size	Light Orientation
<b>PCIWB-32T8-4D</b>	T8 32w	4'	48-1/2" L., 4-1/2" H.,	Downlight
<b>PCIWB-32T8-4UD</b>			7-1/16" W.	Uplight & Downlight




## Flourescent Strip

Product No.	Finish	Lamps	Lumens	Size
<b>P7265-30EB</b>	White, Baked Enamel	1 17w T8		24" L., 3-3/8" H., 3" W.
<b>P7266-30EB</b>		2 17w T8		
<b>P7267-30EB</b>		1 32w T8		48" L., 3-3/8" H., 3" W.
<b>P7268-30EB</b>		2 32w T8		



## Open LED Striplight

Product No.	Lamp Type	Lumens	Nom. Length	Size	Color Temperature
<b>PCIOS-LED-2-35K</b>	LED 26w	3000	2'	48" L., 1-13/6" H., 47/16" W.	3500K
<b>PCIOS-LED-4-35K</b>	LED 48w	5600	4'	96" L., 1-13/6" H., 47/16" W.	



## Slim Line Wrap



Product No.	Finish	Lamps	Size
<b>P7137-30STR</b>	White	2 F17 T8	26-3/4" L., 2-1/2" H., 6-1/4" W.
<b>P7154-30STR</b>		2 F25 T8	38-3/4" L., 2-5/8" H., 6-1/4" W.
<b>P7189-30STR</b>		2 F32 T8	50-5/8" L., 2-1/2" H., 6-1/4" W.



## LED Lensed Strip Light

Product No.	Lamp Type	Lamp Size	Lumens	Size	Color Temperature
<b>PCILS-LED-4-35K</b>	LED 53w	4'	5000	48" L., 4-7/16" H., 6" W.	3500K



## Stairwell Luminaire

Product No.	Lamp Type	Lumens	Description	Size	Color Temperature
<b>PCISW-LED-4-35K</b>	LED 52W	5000	52w LED Stairwell Light	54" L., 4" H., 6" W.	3500K
<b>PCISW-32T8-4</b>	32-T8 32W		T-8 Stairwell Light		



## LED Linear Vapor Tight

Product No.	Lamp Type	Lumens	Size	Color Temperature
<b>PCIVT-LED-4-35K</b>	LED 37W	4000	51-3/4" L., 3-7/8" H., 4-1/2" W.	3500K
<b>PCIPG-LED-4-40K</b>	LED 47W	5100	51-2/3" L., 5-5/8" H., 6-7/9" W.	4000K



## LED Retrofit Kit



Product No.	Size	Color Temp.	Lumens	Wattage
<b>PCIRK</b>	<b>22</b> - 2 x 2	<b>30K</b> - 3000K	<b>2000</b> (2 x 2 only)	20W
		<b>35K</b> - 3500K	<b>4000</b> (2 x 2 only)	48W
	<b>24</b> - 2 x 4		<b>3000</b> (2 x 2 / 2 x 4)	33/27W
			<b>3600</b> (2 x 4 only)	33W
			<b>4200</b> (2 x 4 only)	37W

## Fluorescent Emergency Battery Pack



Product No.	Lumens	Wattage
<b>PEEMB-1400L</b>	1400	2.5W
<b>PEEMB-700L</b>	700	3.7W
<b>PEEMB-500L</b>	500	3.7W



## Surface Mount Circline Fluorescent

SURFACE MOUNT CIRCLINE FLUORESCENT WITH CLEAN MODERN LINES AND WHITE ACRYLIC DIFFUSER. 120V NPF ELECTRONIC BALLAST.

Product No.	Finish	Size	Ballast	Lamps
<b>P7249-09EBWB</b> <b>P7249-174EBWB</b>	Brushed Nickel Urban Bronze	10-3/8" dia., 3-1/2" ht.	120 NPF electronic	1 22w T-9
<b>P7250-09EBWB</b> <b>P7250-174EBWB</b>	Brushed Nickel Urban Bronze	17-5/8" dia., 4-1/2" ht.	120 NPF electronic	1 22w T-9 & 1 32w T-9
<b>P7251-09EBWB</b> <b>P7251-174EBWB</b>	Brushed Nickel Urban Bronze	32-1/4" L., 18" W., 4-3/8" ht.	120 NPF electronic	2 32w T-9
<b>P7252-09EBWB</b> <b>P7252-74EBWB</b>	Brushed Nickel Urban Bronze	32-1/4" diam., 6-1/2" ht.	120 NPF electronic	3 32w T-9



P7251-174EBWB



P7252-09EBWB



P7250-09EBWB



P7249-174EBWB



P7250-174EBWB



P7249-09EBWB

## Surface Mount Linear Fluorescent

SURFACE MOUNT LINEAR FLUORESCENT. 120V NPF ELECTRONIC BALLAST.



P7258-09EB



P7258-174EB

Product No.	Finish	Size	Ballast	Lamps
<b>P7258-09EB</b> <b>P7258-174EB</b>	Brushed Nickel w/ white acrylic Urban Bronze w/ white acrylic	48-1/2" L., 11-5/8" ht.	120 NPF electronic	3 F32T8

## Domes

CONTOURED WHITE ACRYLIC DOMES WITH CURVED, TEXTURED WHITE MOLDING. FLOATS 3/4" FROM CEILING, CREATING A HALO EFFECT.




P7206-30EB

Product No.	Finish	Size	Ballast	Lamps
<b>P7206-30EB</b>	White	59" L., 21" W., 6-5/8" ht.	120V HPF electronic	4 F32T8

## Soft Clouds

CONTOURED, SHALLOW WHITE ACRYLIC CLOUDS. DIFFUSER SUSPENDED FROM WHITE CHASSIS.



P7279-60EB

Product No.	Finish	Size	Ballast	Lamps
<b>P7278-60EB</b>	White	28" L., 18" W., 4-5/8" ht.	120V HPF electronic	4 F17T8
<b>P7279-60EB</b>		52" L., 12" W., 4-5/8" ht.		2 F32T8
<b>P7280-60EB</b>		52" L., 18" W., 4-5/8" ht.		4 F32T8
<b>P7285-60EB</b>		30-3/4" L., 27-1/4" W., 5" ht.		2 FB32T8



P7285-60EB



P7278-60EB

## Ribbed Linear Fluorescent

ETCHED RIBBED GLASS DIFFUSER. 120V NPF BALLAST. CEILING MOUNT.

Product No.	Finish	Description	Size	Ballast	Lamps
<b>P7218-09EB</b>	Brushed Nickel	Two-light	25" W., 4" ht., Extends 6-1/4".	120V NPF electronic	2 F17T8
<b>P7221-09EB</b>	Nickel		49" W., 4" ht., Extends 6-1/4".		2 F32T8



P7218-09EB



P7221-09EB





## Exit / Emergency

Our LED exit signs and emergency lighting units, that include remote emergency lights, battery packs and central lighting inverter options, address a wide range of commercial applications to enhance safety and ensure security in your facilities.





PETPE-UR-30-RC  
PETPE -UG-30-RC

## LED Exit Sign

The PETPE Series offers quality and value with a compact and attractive LED based emergency exit. The white housing is made of high impact UL flame rated thermoplastic. Snap together canopy, housing, removable chevrons for quick and easy installation. Universal single or double-face. Remote capacity option will run 4 PERHC Series single remote lamp-heads or 2 double PERHC remotes.

Product No.	Face	Color	Finish	Size
<b>PETPE-UR-30</b>	Universal	Red	White	11.6" w., 7.2" ht., 2" d.
<b>PETPE-UR-30-RC</b> Remote Capacity				
<b>PETPE-UG-30</b>		Green		
<b>PETPE-UG-30-RC</b> Remote Capacity				



PECUE-UR-30



PECUE-UG-30

## LED Combo Exit / Emergency Light

The PECUE Series offers quality and value with a compact and attractive LED based combination emergency exit. The white housing and lamp-heads are made of high impact UL flame rated thermoplastic. Snap together canopy, housing, removable chevrons for quick and easy installation. Universal single or double-face. Remote capacity unit will run 4 PERHC Series single remote lamp-heads or 2 double PERHC remotes.

Product No.	Finish	Color	Size	Lumens
<b>PECUE-UG-30</b>	White	Green	18" w. 7.2" ht. 2" d.	101
<b>PECUE-UG-30-RC</b> Remote Capacity				
<b>PECUE-UR-30</b>		Red		
<b>PECUE-UR-30-RC</b> Remote Capacity				



PE2EU-30

## LED Emergency Light

The PE2EU Series offers quality and value with a compact and attractive LED based emergency light. The white housing and lamp-heads are fully adjustable and glare-free. Snap together design for quick and easy installation with option of Wall or Ceiling mount. Remote capacity unit will run a double-head remote or 2 single-head remotes of the PERHC Series.

Product No.	Finish	Input	Size	Lumens
<b>PE2EU-30</b>	White	120 or 277V AC input	9" w., 4" ht., 2.75" d.	101
<b>PE2EU-30-RC</b> Remote Capacity				



PERHC-SG-ID-30



PERHC-DB-OD-30

## LED Indoor/Outdoor Remote Heads

The PERHC Series offers quality and value with a compact and attractive LED based remote emergency light. Lamp-heads are fully adjustable and glare-free. The remote lamps are driven by the Progress remote capacity Exit combo or Emergency Light. The Outdoor Remote lamp-heads are fully gasketed and weatherproof to ensure operation in wet environments. Can be used with PETPE, PE2EU, and PECUE remote capacity models

Product No.	Finish	Location	Lamp	Size	Lumens
<b>PERHC-SG-ID-30</b>	White	Indoor	Single	4.6" w., 4.6" ht., 2.6" d.	52
<b>PERHC-DB-ID-30</b>			Double	6.7" w., 4.7" ht., 2.5" d.	101
<b>PERHC-SG-OD-30</b>		Outdoor	Single	4.5" w., 4.5" ht., 6.7" d.	52
<b>PERHC-DB-OD-30</b>			Double	7.4" w., 4.5" ht., 5.6" d.	101



PEESE-SR-16  
Surface Mount



Wall Mount Shown



PEERE-SR-16  
Recessed Ceiling Mount Shown

## Edge-Lit LED Emergency Exit

The PEESE/PEERE Series offers quality and value with an Edge-Lit based emergency exit. The PEESE/PEERE is ideal for architectural applications and offers surface and recessed mounting options. The acrylic panels are ultrasonically welded and taped at the edges to maximize illumination and visibility. The Exit panel can be ratcheted to various angles for mounting to angled surfaces. The housing finish and trim-plate is brushed aluminum. Recessed mount model comes with a full recessed box complete with integrated caddy-bar assembly. Surface mount model has a clam-shell design for easy installation and access to internal circuitry. Canopy and mounting hardware included. All models are for emergency operation complete with a NiCad battery, status LED and Push-to-Test switch.

Product No.	Finish	Side / Color	Mount	Size
<b>PEESE-DG-16</b>	Brushed Aluminum	Double / Green	Surface	13" w., 9.6" ht., 3.5" d.
<b>PEESE-DR-16</b>		Double / Red		
<b>PEESE-SG-16</b>		Single / Green		
<b>PEESE-SR-16</b>		Single / Red		

Product No.	Finish	Side / Color	Mount	Size
<b>PEERE-DG-16</b>	Brushed Aluminum	Double / Green	Recessed	12.7" w., 7.5" ht., 4" d.
<b>PEERE-DR-16</b>		Double / Red		
<b>PEERE-SG-16</b>		Single / Green		
<b>PEERE-SR-16</b>		Single / Red		



PEALE-SG-EM-16  
PEALE-SR-EM-16

## LED Aluminum Exit Sign

The PEALE Series offers quality and value with a compact and attractive Thin Die-Cast aluminum Exit sign. Exit face illumination by low energy, long-life red or green ultra bright LED's. The Exit face-plate is brushed aluminum with black edges and 6" letters with a red or green diffuser. Single-face models can be wall, end or ceiling mounted. Double-face models are end or ceiling mounted only. Includes canopy, universal mounting plate and a battery for emergency operation. Test switch and AC-on indicator are located at bottom center. Directional indication made by knock-out chevrons.

Product No.	Finish	Side / Color	Size
<b>PEALE-DG-EM-16</b>	Brushed Aluminum	Double / Green	11.6" w., 7.75" ht., .875" d.
<b>PEALE-DR-EM-16</b>		Double / Red	
<b>PEALE-SG-EM-16</b>		Single / Green	
<b>PEALE-SR-EM-16</b>		Single / Red	



PEWLE-SG-30  
PEWLE-SR-30

## LED Wet Location Exit Sign

The PEWLE Series offers quality and value with a wet location rated emergency Exit sign. Housing and face-plate made from impact resistant UV stabilized polycarbonate. Housing is corrosion resistant and face-plate is fully gasketed. Exit face illumination by low energy, long-life red or green ultra bright LED's. The Exit letters measure 6" with a red or green diffuser. Single-face models can be wall mounted by use of molded-in template, end or ceiling mounted. Double-face models are end or ceiling mounted only. Includes canopy and universal mounting plate. Water-proof test switch and AC-on indicator located at Exit bottom. Directional indication made by place-able chevrons. Conduit entry KO's located in top and side housing, with conduit fitting included.

Product No.	Finish	Side / Color	Size
<b>PEWLE-SR-30</b>	White	Single / Red	12.5" w., 8.5" ht., 2.5" d.
<b>PEWLE-DR-30</b>		Double / Red	
<b>PEWLE-SG-30</b>		Single / Green	
<b>PEWLE-DG-30</b>		Double / Green	



PEHWU-82

## Wet Location Emergency Light

The PEHWU-82 is a wet location listed emergency lighting unit. The housing is made of injection molded, flame retardant thermoplastic with a gray finish. The heads are fully adjustable and each contain two 6VDC, 7 watt halogen lamps and are integrated inside and a protected by a fully-gasketed and high impact poly-carbonate shield. The back housing contains a molded-in template for wall mounting to any standard universal J-Box. Front cover is secured with 2 gasketed crews.

Product No.	Finish	Input	Lamp	Size
<b>PEHWU-82</b>	Metallic Gray	120/277V	MR-16 Halogen	14.9" w., 5.7" ht., 4.2" d.





PE2WL-82

## Wet Location LED Emergency Light

The PE2WL offers LED performance and value with a compact and attractive wet location LED based emergency light. The grey housing is made of corrosion resistant UV stabilized polycarbonate. Lamp-head consists of metalized high-performance reflector and 15 ultra-bright LED's with tempered glass lens. Includes external mounting brackets for ease of installation. The Pe2wl has adequate capacity to run 1 each PEWLH double head or 2 PEWLH single-head remotes at 9.6 VDC for 90 minutes.

Product No.	Finish	Input	Size
<b>PE2WL-82</b>	Metallic Grey	120 or 277V AC input	8" w., 12" ht.



PEWLH-SG-82

### Accessories

Product No.	Description	Finish
<b>PEWLH-SG-82</b>	Single Head	Metallic Grey
<b>PEWLH-DB-82</b>	Double Head	



PEOEU-EM-20

## Normally On/Off Outdoor Emergency

The PEOEU Series offers LED performance in "normally on" AC and emergency lighting modes. The unit has a prismatic polycarbonate refractor with a durable die-cast aluminum housing available with durable powder coated finish in dark bronze, nickel or white. The housing is fully sealed and gasketed. It is designed for wall mounting with a universal K/O pattern in the back-plate for installation to most standard size junction boxes. Illumination is provided by 2 high power LEDs driven at 3 watts each. LED color at 5500K.

Series	Description	Finish	Size	Lumens
<b>PEOEU-EM-09</b>	Emergency Battery	Brushed Nickel	6.54" w., 10.47" ht., 3.78" d.	AC Mode - 223
<b>PEOEU-EM-20</b>		Bronze		
<b>PEOEU-EM-30</b>		White		
<b>PEOEU-EM-09-HTR</b>	Emergency Battery w/ heater option	Brushed Nickel		DC Mode - 261 (Running on Emergency Battery)
<b>PEOEU-EM-20-HTR</b>		Bronze		
<b>PEOEU-EM-30-HTR</b>		White		



## Fluorescent Emergency Battery Pack

Product No.	Lumens	Wattage
<b>PEEMB-1400L</b>	1400	2.5W
<b>PEEMB-700L</b>	700	3.7W
<b>PEEMB-500L</b>	500	3.7W



PECLB-32-30-S



PECLB-55-30-T

## Central Lighting Micro Inverter

Designed for indoor installation in commercial or industrial applications, the PECLB Series micro inverter system provides Emergency AC power to lighting fixtures equipped with incandescent, fluorescent, CFL or LED lamps between 32 and 55 watts for 90 minutes. The lighting load can be installed at a distance of up to 1000 feet from the micro inverter. The enclosure is constructed of heavy-duty, 20 gauge steel with a white powder-coat finish.

Product No.	Finish	Capacity	Mount	Size
<b>PECLB-32-30-S</b>	White	32w	Surface	14.75" w., 7.38" ht., 3.13" d.
<b>PECLB-32-30-T</b>			Recessed T-Bar	23.88" w., 8" ht., 6.19" d.
<b>PECLB-55-30-S</b>		55w	Surface	14.75" w., 7.38" ht., 4.38" d.
<b>PECLB-55-30-T</b>			Recessed T-Bar	23.88" w., 8" ht., 6.19" d.



## Close To Ceiling

Overhead lighting, such as close-to-ceiling fixtures, provide general illumination for interior spaces in apartment communities, townhomes, mixed-use residential facilities and more. Decorative LED and CFL surface mount options reflect the latest design trends, while also providing energy efficient benefits.



# Mini Flush Mount


THE LED FLUSH MOUNT SERIES USES AN INTUITIVE SNAP-IN SYSTEM THAT MAKES FLUSH MOUNT INSTALLATION EASIER THAN EVER. SIMPLY, INSTALL ADAPTER ONTO JUNCTION BOX, THEN SNAP INTO PLACE USING THE FLUSH MOUNT CLIP.

### FEATURES

- Flicker free dimming with many ELV dimmers
- Wet location listed
- 3000K color temperature
- 90+CRI
- 120v input voltage AC
- TM-21 60,000 hr. life
- 17w: 1035 delivered Lumens, 60 Lumens/watt
- 12w: 630 delivered Lumens, 52.5 Lumens/watt
- 10.5w: 670 delivered Lumens, 63.8 Lumens/watt
- CA Title 24 Compliant

### SURFACE and RECESSED INSTALLATION HARDWARE

Included adjustable mounting option that fits 6", 5" or 4" recessed housing. The fixture also includes an E26 Edison Base adapter for a retrofit screw-in option. This hardware is included in **P8022** and **P8027** series.



# Flush Mount / Recessed



P8022-20/30K9-AC1-L10

Product No.	Finish	Description	Size	Lamp *included
<b>P8022-20/30K9-AC1-L10</b>	Antique Bronze	One-light	7-1/4" dia., 1-1/4" ht.	*One 17w LED module
<b>P8022-28/30K9-AC1-L10</b>	White			
<b>P8022-31/30K9-AC1-L10</b>	Black			
<b>P8022-82/30K9-AC1-L10</b>	Metallic Gray			



P8022-28/30K9-AC1-L10



P8022-31/30K9-AC1-L10



P8022-82/30K9-AC1-L10



P8027-82/30K9-AC1-L10

Product No.	Finish	Description	Size	Lamp *included
<b>P8027-20/30K9-AC1-L10</b>	Antique Bronze	One-light	7-1/4" dia., 1-1/4" ht.	*One 17w LED module
<b>P8027-28/30K9-AC1-L10</b>	White			
<b>P8027-31/30K9-AC1-L10</b>	Black			
<b>P8027-82/30K9-AC1-L10</b>	Metallic Gray			



P8027-20/30K9-AC1-L10



P8027-31/30K9-AC1-L10



P8027-28/30K9-AC1-L10





P8222-28/30K9-AC1-L10

## Flush Mount (no recessed hardware)



Product No.	Finish	Description	Size	Lamp *included
<b>P8222-28/30K9-AC1-L10</b>	White	One-light flush mount only	7-1/4" dia., 1-1/4" ht.	*One 17w LED module

### RECESSED ADAPTERS

Product No.	<b>P8595-01</b>
Description	Hardware for <b>P8222</b> to make it available for recessed installation. Mounting option fits 6", 5" or 4" recessed housings. Edison base adapter included.
Size	5-3/16" w, 3-9/16" ht.



P8107-28/30K9



## LED Slim-Line Surface Mount



Product No.	Finish	Description	Size	Lamp
<b>P8107-09/30K</b>	Brushed Nickel	Requires minimum 2" box.	5-1/2" W., 2-3/4" ht.	1 12w LED
<b>P8107-20/30K</b>	Antique Bronze			
<b>P8107-28/30K</b>	White			
<b>P8107-31/30K</b>	Black			

#### FEATURES

- Flicker free dimming with most ELV dimmers
- Wet location listed
- 90+ CRI
- 120V input voltage AC
- 60,000 hr. life
- 12w: 630 delivered lumens, 52.5 lumens per watt
- CA Title 24 Compliant



2" box minimum

Bracket for P8107-28/30K9 shown mounted into JBox. JBox not included.

FEATURES

- Flicker free dimming with many ELV dimmers
- Wet location listed
- 3000K color temperature
- 90+CRI
- 120v input voltage AC
- TM-21 60,000 hr. life
- 17w: 1035 delivered Lumens, 60 Lumens/watt
- 12w: 630 delivered Lumens, 52.5 Lumens/watt
- 10.5w: 670 delivered Lumens, 63.8 Lumens/watt
- CA Title 24 Compliant

## 5" Flush Mount / Recessed



P8240-31/30K9-AC1-L06

Product No.	Finish	Description	Size	Lamp *included
<b>P8240-20/30K9-AC1-L06</b>	Antique Bronze	One-light	5-1/2" dia., 1-1/4" ht.	*One 12w LED module
<b>P8240-28/30K9-AC1-L06</b>	White			
<b>P8240-31/30K9-AC1-L06</b>	Black			
<b>P8240-82/30K9-AC1-L06</b>	Metallic Gray			



P8240-20/30K9-AC1-L06



P8240-28/30K9-AC1-L06



P8240-82/30K9-AC1-L06



P8241-20/30K9-AC1-L06

Product No.	Finish	Description	Size	Lamp *included
<b>P8241-20/30K9-AC1-L06</b>	Antique Bronze	One-light	5-1/4" dia., 1-1/4" ht.	*One 10.5w LED module
<b>P8241-28/30K9-AC1-L06</b>	White			
<b>P8241-31/30K9-AC1-L06</b>	Black			
<b>P8241-82/30K9-AC1-L06</b>	Metallic Gray			



P8241-28/30K9-AC1-L06



P8241-31/30K9-AC1-L06



P8241-82/30K9-AC1-L06



P8247-31/30K9-AC1-L06

Product No.	Finish	Description	Size	Lamp *included
<b>P8247-09/30K9-AC1-L06</b>	Antique Bronze	One-light with etched glass diffuser	5-1/2" dia., 1-1/2" ht.	*One 12w LED module
<b>P8247-20/30K9-AC1-L06</b>	White			
<b>P8247-28/30K9-AC1-L06</b>	Black			
<b>P8247-31/30K9-AC1-L06</b>	Metallic Gray			



P8247-09/30K9-AC1-L06



P8247-20/30K9-AC1-L06



P8247-28/30K9-AC1-L06



P8147-28/30K9

## 7" LED Decorative Surface Mount



Product No.	Finish	Description	Size	Lamp
<b>P8147-09/30K</b>	Brushed Nickel	Round with etched glass	7-1/4" W., 2-3/4" ht.	1 17w LED
<b>P8147-20/30K</b>	Antique Bronze			
<b>P8147-28/30K</b>	White			
<b>P8147-31/30K</b>	Black			

FEATURES

- 120V AC Replaceable LED module
- 1211 source lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

Portal

Product No.	Finish	Description	Size	Lamp *included
<b>P3658-0930K9</b>	Brushed Nickel	Etched glass with industrial inspired accents	11" dia., 3-3/4" ht.	*One 17w LED module
<b>P3658-2030K9</b>	Antique Bronze		11" dia., 3-3/4" ht.	
<b>P3659-0930K9</b>	Brushed Nickel	14" dia., 5-1/8" ht.	14" dia., 5-1/8" ht.	
<b>P3659-2030K9</b>	Antique Bronze			



P3658-0930K9



P3659-2030K9



P3658-2030K9



P3659-0930K9

FEATURES

- 120V AC Replaceable LED module
- 1211 source lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant
- Wall or Ceiling Mount

Helm ADA

Product No.	Finish	Description	Size	Lamp *included
<b>P3447-0930K9</b>	Brushed Nickel	One-light w/ white acrylic diffuser	11" sq., 3-3/4" ht.	*One 17w LED module
<b>P3447-2030K9</b>	Antique Bronze			
<b>P3448-0930K9</b>	Brushed Nickel	Two-light with white acrylic diffuser	14" sq., 3-3/4" ht.	*Two 17w LED modules
<b>P3448-2030K9</b>	Antique Bronze			
<b>P3449-0930K9</b>	Brushed Nickel	Three-light with white acrylic diffuser	18" sq., 3-3/4" ht	*Three 17w LED modules
<b>P3449-2030K9</b>	Antique Bronze			



P3447-0930K9



P3448-2030K9



P3449-0930K9



P3449-0930K9



P3449-2030K9



P3447-2030K9



# Weaver

## FEATURES

- 120V AC Replaceable LED module
- 1211 source lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant
- Wall or Ceiling Mount



P3610-0930K9



P3610-2030K9

Product No.	Finish	Description	Size	Lamp *included	ADA
<b>P3610-0930K9</b>	Brushed Nickel	One-light flush mount with linen glass diffuser surrounded by a linen shade	10" dia., 3-1/2" ht.	*One 17w LED module	Y
<b>P3610-2030K9</b>	Antique Bronze				
<b>P3611-0930K9</b>	Brushed Nickel	Two-light flush mount with linen glass diffuser surrounded by a linen shade	16" dia., 4" ht.	*Two 17w LED modules	Y
<b>P3611-2030K9</b>	Antique Bronze				
<b>P3612-0930K9</b>	Brushed Nickel	Three-light flush mount with linen glass diffuser surrounded by a linen shade	22" sq., 4-1/2" ht	*Three 17w LED modules	N
<b>P3612-2030K9</b>	Antique Bronze				



P3611-0930K9



P3611-2030K9



P3612-0930K9



P3612-2030K9

# Transit <sup>ADA</sup>



P3411-0930K9



P3411-2030K9

Product No.	Finish	Description	Size	Lamp *included
<b>P3411-0930K9</b>	Brushed Nickel	One-light w/ white acrylic diffuser	11" sq., 3-3/4" ht.	*One 17w LED module
<b>P3411-2030K9</b>	Antique Bronze			
<b>P3417-0930K9</b>	Brushed Nickel	Two-light with white acrylic diffuser	14" sq., 3-3/4" ht.	*Two 17w LED modules
<b>P3417-2030K9</b>	Antique Bronze			
<b>P3432-0930K9</b>	Brushed Nickel	Three-light with white acrylic diffuser	18" sq., 3-3/4" ht	*Three 17w LED modules
<b>P3432-2030K9</b>	Antique Bronze			



P3417-0930K9



P3432-0930K9



P3417-2030K9



P3432-2030K9

# Bingo ADA

**FEATURES**

- 120V AC Replaceable LED module
- 1211 source lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant
- Wall or Ceiling Mount



Product No.	Finish	Description	Size	Lamps *included
<b>P3695-0930K9</b> <b>P3695-7430K9</b>	Brushed Nickel Venetian Bronze	Three-light with white acrylic diffuser	40" L., 11-5/8" W., 3-3/8" ht.	*Three 17w LED modules



P3695-0930K9



P3695-7430K9


# Beyond WALL OR CEILING MOUNT.



Product No.	Finish	Description	Size	Lamp *included
<b>P2306-0930K9</b>	Brushed Nickel	One-light with geometric glass and acrylic diffuser	12" sq. 6" ht.	*One 17w LED module
<b>P2307-0930K9</b>		One-light with textured glass and acrylic diffuser	12" dia. 6 ht.	
<b>P2308-0930K9</b>		One-light with acrylic diffuser. White, bronze and brushed nickel knobs included	12" dia. 6 ht.	
<b>P2309-0930K9</b>		One-light with acrylic diffuser. White, bronze and brushed nickel knobs included	12" sq. 6" ht.	
<b>P2310-0930K9</b>		One-light with etched glass diffuser and brushed metal shade	10" dia. 5 ht.	
<b>P2311-0930K9</b>		One-light with acrylic diffuser. White, bronze and brushed nickel knobs included	12" dia. 6 ht.	



P2306-0930K9



P2307-0930K9



P2308-0930K9



P2309-0930K9



P2310-0930K9



P2311-0930K9

# Round Cloud



Product No.	Finish	Description	Size	Ballast	Lamp *included
<b>P7385-3030K9</b>	White	One-light	10-7/8" dia., 3-1/4" ht.	120V NPF	*One 17w integral LED module



P7385-30

# Maier



Product No.	Finish	Description	Size	Lamps *included
<b>P3675-0930K9</b>	Brushed Nickel	Three-light with white acrylic diffuser	18" dia., 5-1/2" ht.	*Three 17w LED modules
<b>P3675-2030K9</b>	Antique Bronze			
<b>P3675-3030K9</b>	White			
<b>P3910-0930K9</b>	Brushed Nickel	One-light with white acrylic diffuser	9" dia., 4-3/8" ht.	*One 17w LED module
<b>P3910-2030K9</b>	Antique Bronze			
<b>P3910-3030K9</b>	White			
<b>P3911-0930K9</b>	Brushed Nickel	Two-light with white acrylic diffuser	14" dia., 4-3/4" ht.	*Two 17w LED modules
<b>P3911-2030K9</b>	Antique Bronze			
<b>P3911-3030K9</b>	White			



P3675-0930K9



P3675-2030K9



P3675-3030K9



P3910-0930K9



P3910-2030K9



P3911-0930K9



P3911-2030K9



P3910-3030K9



P3911-3030K9

# Milford



Product No.	Finish	Description	Size	Lamp *included
<b>P3665-2030K9</b>	Antique Bronze	One-light flush mount with etched glass shade	8-5/8" dia., 4-1/8" ht.	*One 17w integral LED module
<b>P3665-3130K9</b>	Black		10-5/8" dia., 4-7/8" ht.	
<b>P3673-2030K9</b>	Antique Bronze			
<b>P3673-3130K9</b>	Black			



P3665-2030K9



P3665-3130K9



P3673-2030K9



P3673-3130K9

# 6" Fitter



Product No.	Finish	Description	Size	Lamp *included
<b>P3408-0930K9</b>	Brushed Nickel	One-light with white opal glass diffuser	0-7/8" dia., 3-1/4" ht.	*One 17w LED module
<b>P3408-2030K9</b>	Antique Bronze			
<b>P3408-3030K9</b>	White			



P3408-0930K9



P3408-2030K9




P3408-3030K9

# Flush Mounts

## FEATURES

- 120V AC Replaceable LED module
- 1211 source lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

## ETCHED GLASS

Product No.	<b>P2302-0930K9</b> Brushed Nickel <b>P2302-2030K9</b> Antique Bronze	
Description	One-light	
Size	11" dia., 4" ht.	
Lamp	One 17w LED module included	


P2302-0930K9



P2302-2030K9



## UMBER GLASS

Product No.	<b>P2303-0930K9</b> Brushed Nickel <b>P2303-2030K9</b> Antique Bronze	
Description	One-light	
Size	13-1/4" dia., 4-3/4" ht.	
Lamp	One 17w LED module included	


P2303-0930K9



P2303-2030K9




## UMBER GLASS

Product No.	<b>P2321-2030K9</b> Antique Bronze with umber glass	
Description	One-light	
Size	11 dia., 4" ht.	
Lamp	One 17w LED module included	

P2321-2030K9



Product No.	<b>P2322-2030K9</b> Antique Bronze with umber glass	
Description	One-light	
Size	13-1/4 dia., 4-3/4" ht.	
Lamp	One 17w LED module included	

P2322-2030K9





ETCHED GLASS

Product No. **P2300-0930K9** Brushed Nickel  
**P2300-2030K9** Antique Bronze



Description One-light

Size 11" dia., 4-1/4" ht.

Lamp One 17w LED module included

P2300-0930K9



P2300-2030K9



Product No. **P2301-0930K9** Brushed Nickel  
**P2301-2030K9** Antique Bronze



Description One-light

Size 12-1/2" dia., 4-1/2" ht.

Lamp One 17w LED module included

P2301-0930K9



P2301-2030K9



WHITE RIBBED GLASS

Product No. **P2304-0930K9** Brushed Nickel  
**P2304-2030K9** Antique Bronze  
**P2304-3030K9** White



Description One-light

Size 11-3/8" dia., 5-3/4" ht.

Lamp One 17w LED module included

P2304-0930K9



P2304-2030K9



P2304-3030K9



Product No. **P2305-0930K9** Brushed Nickel  
**P2305-2030K9** Antique Bronze  
**P2305-3030K9** White



Description One-light

Size 13" dia., 6-3/4" ht.

Lamp One 17w LED module included

P2305-0930K9



P2305-2030K9



P2305-3030K9



# Eclipse

Brushed Nickel, Polished Brass and Antique Bronze finishes feature satin opal glass.



P3489-20EB



P3564-10EB



P3562-09EB



P3570-10EB

Product No.	Finish	Size	Ballast	Lamps
<b>P3489-20EB</b>	Antique Bronze	15-1/4" dia., 4-1/8" ht.	120V/277V HPF electronic	2 13w 4-pin Quad CFL. G24q-1 base.
<b>P3562-09EB</b>	Brushed Nickel			
<b>P3562-10EB</b>	Polished Brass			
<b>P3564-09EB</b>	Brushed Nickel	19-3/8" dia., 5-1/2" ht.		3 13w 4-pin Quad CFL. G24q-1 base.
<b>P3564-10EB</b>	Polished Brass			
<b>P3491-20EB</b>	Antique Bronze	27-3/8" dia., 7-1/8" ht.		4 13w 4-pin Quad CFL. G24q-1 base.



P3562-10EB



P3564-09EB



P3491-20EB

Product No.	Finish	Size	Ballast	Lamp *included
<b>P3492-20EB</b>	Antique Bronze	15-1/4" dia., 10-5/8" ht.	120V/277V HPF electronic	2 26w 4-pin Quad CFL. G24q-3 base.
<b>P3568-09EB</b>	Brushed Nickel			
<b>P3570-09EB</b>	Brushed Nickel	19-3/8" dia., 13-1/4" ht.		3 26w 4-pin Quad CFL. G24q-1 base.



P3492-20EB



P3468-09EB



P7315-20WB



P7325-10WB



P7324-09WB



P7327-09WB

Product No.	Finish	Size	Ballast	Lamps *included	
<b>P7315-20WB</b>	Antique Bronze	15-1/4" dia., 4-1/8" ht.	120V NPF electronic	*2 13w 4-pin Quad CFL.G24q-1 base.	
<b>P7324-09WB</b>	Brushed Nickel				
<b>P7324-10EBWB</b>	Polished Brass				
<b>P7316-20WB</b>	Antique Bronze	19-3/8" dia., 5-1/2" ht.		120V NPF electronic	*3 13w 4-pin Quad CFL.G24q-1 base.
<b>P7325-09WB</b>	Brushed Nickel				
<b>P7325-10WB</b>	Polished Brass				
<b>P7326-09WB</b>	Brushed Nickel	27-3/8" dia., 7-1/8" ht.	120V NPF electronic		*4 13w 4-pin Quad CFL. G24q-1 base.



P7324-10EBWB



P7316-20WB



P7325-09WB



P7326-09WB

Product No.	Finish	Size	Ballast	Lamps *included		
<b>P7327-09WB</b>	Brushed Nickel	15-1/4" dia., 10-5/8" ht.	120V NPF electronic	*2 13w 4-pin Quad CFL. G24q-1 base.		
<b>P7319-20WB</b>	Antique Bronze	19-3/8" dia., 13-1/4" ht.		120V NPF electronic	*3 26w 4-pin Quad CFL. G24q-3 base.	
<b>P7328-09WB</b>	Brushed Nickel				*3 13w 4-pin Quad CFL. G24q-1 base.	
<b>P7320-20WB</b>	Antique Bronze	27-3/8" dia., 20-1/2" ht.			120V NPF electronic	*4 26w 4-pin Quad CFL. G24q-3 base.
<b>P7329-09WB</b>	Brushed Nickel					*4 26w 4-pin Quad CFL. G24q-1 base.





P3687-09WB



P3687-20WB

# Random

Product No.	Finish	Description	Size	Lamps *included
<b>P3687-09WB</b>	Brushed Nickel	One-light w/ alabaster glass	11-" dia., 5-3/8" ht.	*1 13w GU24 CFL
<b>P3687-20WB</b>	Antique Bronze			
<b>P3997-09WB</b>	Brushed Nickel	One-light w/ etched glass		
<b>P3997-15WB</b>	Polished Chrome			
<b>P3997-20WB</b>	Antique Bronze			
<b>P3998-20WB</b>	Antique Bronze	One-light w/ light etched umber glass		
<b>P3999-20WB</b>	Antique Bronze	One-light w/ light etched umber linen glass		



P3997-20WB



P3997-09WB



P3997-15WB



P3998-20WB



P3999-20WB



P3624-20WB



P3624-09WB

Product No.	Finish	Description	Size	Lamps *included
<b>P3642-09WB</b>	Brushed Nickel	Two-light w/ alabaster glass	14-" dia., 6-5/8" ht.	*2 13w GU24 CFL
<b>P3642-20WB</b>	Antique Bronze			
<b>P3642-09WB</b>	Brushed Nickel	Two-light w/ etched glass		
<b>P3642-15WB</b>	Polished Chrome			
<b>P3642-20WB</b>	Antique Bronze			
<b>P3651-20WB</b>	Antique Bronze	Two-light w/ light etched umber glass		
<b>P3660-20WB</b>	Antique Bronze	Two-light w/ light etched umber linen glass		



P3642-15WB



P3642-09WB



P3642-20WB



P3651-20WB



P3660-20WB

# Random

Product No.	Finish	Description	Size	Lamps *included
<b>P3425-09WB*</b>	Brushed Nickel	Two-light semi-flush w/ alabaster glass	14-" dia., 6-5/8" ht.	*2 13w GU24 CFL
<b>P3425-20WB*</b>	Antique Bronze			
<b>P3426-09WB*</b>	Brushed Nickel	Two-light semi-flush w/ etched glass		
<b>P3426-15WB*</b>	Polished Chrome			
<b>P3426-20WB*</b>	Antique Bronze			
<b>P3427-20WB*</b>	Antique Bronze	Two-light semi-flush w/ light etched umber glass		
<b>P3431-20WB*</b>	Antique Bronze	Two-light semi-flush w/ light etched umber linen glass		



P3427-20WB



P3426-15WB



P3431-20WB



P3426-20WB



P3426-09WB



P3425-20WB



P3425-09WB

\* Semi-flush fixtures include mounting hardware for both stem and ceiling mount



P3527-20WB



P3804-09WB



P3803-09WB

Product No.	Finish	Description	Size	Lamps *included
<b>P3527-20WB</b>	Antique Bronze	Three-light w/ etched glass	16-1/2" dia., 6-3/8" ht.	*3 13w GU24 CFL
<b>P3602-20WB</b>				*3 18w GU24 CFL
<b>P3803-09WB</b>	Brushed Nickel	Three-light w/ linen etched umber glass		*3 13w GU24 CFL
<b>P3803-20WB</b>	Antique Bronze			
<b>P3804-09WB</b>	Brushed Nickel			
<b>P3804-15WB</b>	Polished Chrome	Three-light w/ alabaster glass		
<b>P3804-20WB</b>	Antique Bronze	Three-light w/ etched glass		



P3804-20WB



P3804-15WB



P3602-20WB




P3803-20WB






## Round Clouds

WHITE CONTOURED ACRYLIC CLOUDS WITH SMOOTH FINISH TEXTURE. TWIST ON INSTALLATION. WALL OR CEILING MOUNT.

Product No.	Finish	Description	Size	Ballast	Lamps	
<b>P7383-30</b>	White	Two-light	14-3/8" dia., 3-5/8" ht.	120V NPF	1 22w FC8T9 circline & 1 32w FC12T9 circline	ADA
<b>P7384-30</b>			18-1/8" dia., 4-1/8" ht.		1 32w FC12T9 circline & 1 40w FC16T9 circline	
<b>P7384-30WB</b>		Four-light	18" dia., 4-1/8" ht.		4 13w GU24 CFL (included)	
<b>P7385-30</b>		One-light	10-7/8" dia., 3-1/4" ht.		1 22w FC8T9 circline	ADA 

## Round Clouds

WHITE CONTOURED ACRYLIC CLOUDS.


Product No.	Finish	Description	Size	Lamps	*included	ADA 
<b>P3433-30WB</b>	White	One-light	10-7/8" dia., 3-1/4" ht.	*One GU24 CFL lamps, each 13w max.		
<b>P3637-30WB</b>		Two-light	14" dia., 3-5/8" ht.	*Two GU24 CFL lamps, each 13w max.		



## Round Clouds

WHITE CONTOURED ACRYLIC CLOUDS SUSPEND OVERHEAD WITH A ROUNDED FINISH. REGRESSED CHASSIS. WALL OR CEILING MOUNT.

Product No.	Finish	Description	Size	Ballast	Lamps	
<b>P7307-60</b>	White	One-light	16" dia., 4" ht.	120V NPF	1 32w FC12T9 circline	ADA 
<b>P7309-60</b>		Two-light	20" dia., 4-1/2" ht.	120V NPF	1 32w FC12T9 circline & 1 32w FC12T9 circline	
<b>P7310-60EB</b>			16" dia., 4" ht.	120V NPF electronic	2 13w 4-pin Quad CFL G24q-1 base	ADA



## Squares

WHITE ACRYLIC DIFFUSER WITH RECTILINEAR FORMS. REGRESSED WHITE CHASSIS. SWING ACTION LATCHES ON DIFFUSER. WALL OR CEILING MOUNT.

ADA

Product No.	Finish	Description	Size	Ballast	Lamps
<b>P7379-30</b>	White	Two-light	15" sq., 3-1/8" ht.	120V NPF	1 22w FC8T9 circline & 1 32w FC12T9 circline
<b>P7380-30</b>			19" sq., 3-1/8" ht.		1 32w FC12T9 circline 1 40w FC16T9 circline
<b>P7381-30</b>		Three-light	15" sq., 3" ht.		3 13w 2-pin twin CFL GX23 base
<b>P7382-30</b>		Two-light	12-1/2" sq., 3-1/8" ht.		2 13w 2-pin twin CFL GX23 base



P7379-30



P7380-30



P7382-30



P7381-30

## Squares

WHITE POLYCARBONATE DIFFUSER. LOW PROFILE, IMPACT RESISTANT POLYCARBONATE FRAME.

ADA

Product No.	Finish	Description	Size	Ballast	Lamps
<b>P7118-30</b>	White	Two-light	12" sq., 2-1/4" ht.	120V NPF	2 13w 2-pin twin CFL GX23 base
<b>P7182-30</b>			9" sq., 2" ht.		2 7w or 2 9w 2-pin twin CFL GX23 base



P7118-30



P7182-30



## Etched Ribbed Glass



Product No.	Finish	Description	Size	Lamps *included
<b>P3761-09EBWB</b>	Brushed Nickel	One-light	11-1/2" dia., 4-1/2" ht.	*1 13w GU24 CFL
<b>P3762-09EBWB</b>	Nickel	Two-light	14" dia., 4-3/4" ht.	*2 13w GU24 CFL



## Etched Alabaster Glass



Product No.	Finish	Description	Size	Lamps *included
<b>P3760-09EBWB</b>	Brushed Nickel	Two-light	16-3/4" dia., 5-1/2" ht.	*2 18w GU24 CFL
<b>P3764-09EBWB</b>		One-light	11-1/2" dia., 3-3/4" ht.	*1 13w GU24 CFL
<b>P3765-09EBWB</b>		Two-light	14" dia., 4-3/4" ht.	*2 13w GU24 CFL



## Avalon



Product No.	Finish	Description	Size	Lamps *included
<b>P3468-09EBWB</b>	Brushed Nickel	Two-light semi-flush	14-1/2" dia., 14-3/8" ht.	*2 13w GU24 CFL

P3468-09EBWB



## Swirled Glass



Product No.	Finish	Description	Size	Lamps
<b>P3547-30EBWB</b>	Textured White	Two-light	12-3/4" dia., 6" ht.	*2 13w GU24 CFL
<b>P3548-30EBWB</b>	White	Two-light	15-1/2" dia., 6" ht.	*3 13w GU24 CFL

P3548-30EBWB



## Ceiling Fans

Circulate air in any interior or exterior space with ceiling fans that provide functional and decorative elements. Progress Lighting's ceiling fan assortment features a wide range of design styles, as well as options for light kits that add general lighting to a room.



[progresscommercial.com](http://progresscommercial.com)












P2531-20  
Antique Bronze with  
Cherry blades



P2531-09  
Brushed Nickel with  
Natural Cherry blades

## North Park



Product No.	Finish	Reversible Blades	Description	CTC installation	
P2531-09	Brushed Nickel	Natural Cherry 	Cherry 	Size: 52" dia., 16" ht. CTC 11" ht. 30-year limited warranty 45" Canopy SureConnect® System Compatible with universal light kits	
P2531-20	Antique Bronze	Cherry 	Classic Walnut 		

ENERGY INFORMATION AT HIGH SPEED

AIRFLOW: 5,275 cubic feet per minute  
 ELECTRICITY USE: 57 watts (excludes lights)  
 AIRFLOW EFFICIENCY: 93 cubic feet per minute per watt



P2530-09  
Brushed Nickel with  
Silver blades









P2530-20  
Antique Bronze with  
Classic Walnut blades



P2530-30W  
White with white blades

## 54" Signature Plus Fan



Product No.	Finish	Reversible Blades	Description
P2530-09	Brushed Nickel	Silver 	Natural Cherry 
P2530-20	Antique Bronze	Classic Walnut 	Medium Cherry 
P2530-30W	White	White 	White 

ENERGY INFORMATION AT HIGH SPEED

AIRFLOW: 6,210 cubic feet per minute  
 ELECTRICITY USE: 66 watts (excludes lights)  
 AIRFLOW EFFICIENCY: 94 cubic feet per minute per watt





## Trevina

Product No.	Finish	Blades	Description
P2514-09	Brushed Nickel	Silver 	Size: 52" dia., 18" ht. Etched opal glass 30-yr limited warranty Full function remote included Lamp: One mini-can E-11, 100w max. (included)



**Full Function Remote Included**  
Full-range dimming for light  
Three-speed fan operation  
Reverse direction control



P2514-09  
Brushed Nickel with  
Silver blades

### ENERGY INFORMATION AT HIGH SPEED

AIRFLOW:	4,566 cubic feet per minute
ELECTRICITY USE:	55 watts (excludes lights)
AIRFLOW EFFICIENCY:	83 cubic feet per minute per watt

# Light Kits

## Gather

**P2658-09WB** Brushed Nickel  
**P2658-20WB** Antique Bronze  
 Universal-style light kit with quick-connect wiring.  
 Size: 11" dia., 5-1/2" ht.  
 Lamps: Two 13w GU24 CFL, included (non-dimmable).



P2658-09WB



P2658-20WB

## Alabaster Bowl

**P2621-09EBWB** Brushed Nickel  
**P2621-20EBWB** Antique Bronze  
**P2621-30EBWB** White  
 Alabaster glass. Universal-style with quick-connect wiring.  
 Size: 10-3/4" dia. 6" ht.  
 Lamp: Two 13w GU24 CFL, included (non-dimmable).



P2621-09EBWB



P2621-30EBWB



P2621-20EBWB

## Low Profile

**P2602-09EBWB** Brushed Nickel  
**P2602-20EBWB** Antique Bronze  
**P2602-30EBWB** White  
 Opal glass. Universal style with quick-connect wiring.  
 Size: 10-5/8" dia., 3-7/8" ht.  
 Lamps: Two 13w GU24 CFL, included (non-dimmable).



P2602-20EBWB



P2602-09EBWB



P2602-30EBWB

## Schoolhouse

**P2620-30EBWB** White  
 Universal-style with quick-connect wiring.  
 Schoolhouse opal glass.  
 Size: 8-1/4" dia., 7-1/4" ht.  
 Lamp: One 13w GU24 CFL, included (non-dimmable).



P2620-30EBWB



# Sconces

Wall sconces are versatile fixtures that provide functional and aesthetic light output for both interior and exterior spaces. Featuring the latest in finish options and design styling, sconces are available in vintage modern, classic and contemporary styles. Additionally, many ADA options comply with the American Disabilities Act.



FEATURES

- 120V AC Replaceable LED module
- 1211 source lumens, 71.2 lumens per watt
- 90+ CRI
- TM-21 60,000 hr. life
- 3000K color temperature
- Dimmable with many ELV type dimmers
- Energy Star and CA Title 24 Compliant
- ADA - Complies with American Disabilities Act

# ADA Sconces



Product No.	Finish	Description	Size	Lamp *included
<b>P7083-0930K9</b>	Brushed Nickel	White Acrylic	8-7/8" W., 10-5/8" ht. Extends 4". H/CTR 5-3/8".	*1 17w LED module
<b>P7085-0930K9</b>			9-1/2" W., 10-5/8" ht. Extends 3-3/4". H/CTR 10-3/8".	
<b>P7085-0930K9</b>			8" W., 10-5/8" ht. Extends 3-7/8". H/CTR 5-3/8".	



P7083-0930K9



P7085-0930K9



P7088-0930K9



Product No.	Finish	Description	Size	Lamp *included
<b>P7092-0930K9</b>	Brushed Nickel	Etched opal. Enclosed one-piece glass.	8" W., 10-3/4" ht. Extends 4". H/CTR 5-1/2".	*1 17w LED module
<b>P7093-3030K9</b>	White	White Glass. Includes bronze, white and brushed nickel finials.	11-1/4" W., 11-5/16" ht. Extends 3-1/2". H/CTR 3".	

P7092-0930K9



P7093-3030K9  
*Shown with white finial*



P7093-3030K9  
*Shown with brushed nickel finial*



P7093-3030K9  
*Shown with bronze finial*



P7249-09EBWB



P7249-174EBWB

Product No.	Finish	Description	Size	Lamps *included
<b>P7249-09EBWB</b>	Brushed Nickel	White Acrylic.	10-3/8" dia., Extends 3-1/2".	*1 22w 4-pin T-9 CFL. circline.
<b>P7249-174EBWB</b>	Urban Bronze			



# Etched Opal Glass

Product No.	Finish	Description	Size	Ballast	Lamp
<b>P7052-09EB</b> <b>P7052-20EB</b>	Brushed Nickel Antique Bronze	Satin opal glass	7" W., 14" ht. Extends 4". H/CTR 7".	120v NPF electronic	One GU24 base CFL lamp, 26w max.

Product No.	Finish	Description	Size	Lamp
<b>P7068-09</b> <b>P7068-20</b>	Brushed Nickel Antique Bronze	Satin opal glass	7" W., 14" ht. Extends 4". H/CTR 7".	One GU24 base CFL lamp, 26w max.

Product No.	Finish	Description	Size	Lamp
<b>P7081-09</b> <b>P7081-20</b>	Brushed Nickel Antique Bronze	Satin opal glass	4-1/2" W., 13-1/2" ht. Extends 4". H/CTR 9-1/2".	One GU24 base CFL lamp, 26w max.

Product No.	Finish	Description	Size	Lamp
<b>P7082-09</b> <b>P7082-20</b>	Brushed Nickel Antique Bronze	Satin opal glass	5" W., 18" ht. Extends 4". H/CTR 15-3/8".	One GU24 base CFL lamp, 26w max.



P7052-09EB



P7052-20EB



P7068-09



P7068-20



P7081-09



P7081-20



P7082-20



P7082-09





P7163-2030K9

P7163-0930K9

## Dash

ARCHITECTURALLY MODERN LED SCONCES ARE RELEVANT, INCORPORATES A CREATIVE DESIGN TO SHAPE LIGHT ON THE WALL FOR A DRAMATIC EFFECT.



Product No.	Finish	Size	Lamps *included
<b>P7163-0930K9</b>	Brushed Nickel with polished chrome accents	4-1/2" W., 12-1/2" ht. Extends 3-1/4".	*One 9w LED module
<b>P7163-2030K9</b>	Antique Bronze with polished chrome accents	H/CTR 10-1/4".	

- 623 source lumens per module
- 69.2 lumens/watt
- 3000K color temperature
- Dimmable with many ELV type dimmers
- 90+ CRI



P5790-09

## Shelton

WHITE ACRYLIC. MOUNTS VERTICALLY OR HORIZONTALLY. INDOOR OR OUTDOOR. WET LOCATION LISTED.

ADA

Product No.	Finish	Size	Lamp
<b>P5790-09</b>	Brushed Nickel	11" W., 5-5/8" ht. Extends 3-3/4".	1 13w 4-pin CFL. GX24q-3



P7044-09EBWB

## White Glass

ONE-LIGHT ADA SMALL OUTDOOR CFL WALL LANTERN. CAN BE MOUNTED VERTICALLY OR HORIZONTALLY, AS WELL AS INDOORS OR OUTDOORS.

ADA



Product No.	Finish	Size	Ballast	Lamps *included
<b>P7044-09EBWB</b>	Brushed Nickel	14-3/4" W., 9-7/8" ht. Extends 3-7/8". H/CTR 6".	120V NPF	*2 13w 4-pin Quad CFL. G24q-1 base.
<b>P7093-09EBWB</b>		11-1/4" W., 11-5/16" ht. Extends 3-1/2". H/CTR 6".	120V NPF	*2 13w 4-pin Quad CFL. G24q-1 base.



P7093-09EBWB

# Eclipse

ONE-LIGHT WALL SCONCE WITH SATIN WHITE GLASS IS PERFECT FOR RESIDENTIAL AND COMMERCIAL APPLICATIONS.



P7171-09WB

ADA 



P7176-20WB

Product No.	Finish	Size	Ballast	Lamps *included
<b>P7171-09WB</b>	Brushed Nickel	15-1/4" W., 7-1/2" ht. Extends 4". H/CTR 3".	120V NPF electronic	*1 13w 4-pin Quad CFL. G24q-3 base.
<b>P7176-20WB</b>	Antique Bronze	15" W., 7-1/2" ht. Extends 4". H/CTR 3".		*1 26w 4-pin Quad CFL. G24q-3 base.





P5806-09



P5806-20

## Valera

WHITE ACRYLIC DIFFUSER.  
VERTICAL MOUNT ONLY.

Product No.	Finish	Size	Lamps
<b>P5800-09</b> <b>P5800-20</b>	Brushed Nickel Antique Bronze	5-5/8" W., 8-1/8" ht. Extends 4".	1 GU24 CFL. 18w max.
<b>P5801-09</b> <b>P5801-20</b>	Brushed Nickel Antique Bronze	8-5/8" W., 11-1/8" ht. Extends 4".	1 GU24 CFL. 26w max.
<b>P5806-09</b> <b>P5806-20</b>	Brushed Nickel Antique Bronze	5-5/8" W., 16-1/8" ht. Extends 4".	1 GU24 CFL. 18w max.



P5800-09



P5800-20



P5801-09



P5801-20



P5915-16



P5915-20

## Parker

ADA

Product No.	Finish	Description	Size	Lamps
<b>P5914-16</b> <b>P5914-20</b>	Satin Aluminum Antique Bronze	One-light CFL wall sconce. White acrylic diffuser	5-3/8" W., 10-1/4" ht. Extends 4".	1 GU24 CFL. 26w max.
<b>P5915-16</b> <b>P5915-20</b>	Satin Aluminum Antique Bronze	Two-light CFL wall sconce. White acrylic diffuser	5-5/8" W., 16-7/8" ht. Extends 4".	2 GU24 CFL. each 26w max.



P5914-16



P5914-20



P5914-20  
shown without top and  
bottom for interior use.



## Bath and Vanity

Bathroom lighting helps set the mood for a relaxing space to unwind, while also allowing individuals to complete everyday grooming tasks efficiently. To achieve the best design, a layered lighting approach, which requires several complementing and coordinating fixture options, is recommended.



# Arch

ARCH LED IS AN INNOVATIVE SERIES OF ACRYLIC LED WALL SCONCES THAT OPTIMIZES AESTHETIC APPEAL. FROSTED WHITE ACRYLIC LENS. A PERFORATED METAL MESH END CAP DIFFUSES LIGHT ABOVE AND BELOW THE FIXTURE TO PROVIDE EVEN ILLUMINATION.

## FEATURES

- 120v AC Replaceable LED module
- 1211 source lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable with many ELV type dimmers
- Wall or ceiling mount
- Can be installed vertically or horizontally



PROGRESS **LED**



P2061-0930K9

Product No.	Finish	Description	Size	Lamps *included
<b>P2061-0930K9</b>	Brushed Nickel	One-light bath	7-1/4" W., 6" ht. Extends 3". H/CTR 3".	*One 17w LED module
<b>P2062-0930K9</b>	Brushed Nickel	Two-light bath	14-1/2" W., 6" ht. Extends 3". H/CTR 3".	*Two 17w LED modules
<b>P2063-0930K9</b>	Brushed Nickel	Three-light bath	21-3/4" W., 6" ht. Extends 3". H/CTR 3".	*Three 17w LED modules
<b>P2064-0930K9</b>	Brushed Nickel	Four-Light Bath	29" W., 6" ht. Extends 3". H/ CTR 3".	*Four 17w LED modules



P2062-0930K9



P2063-0930K9



P2064-0930K9



P2061-0930K9  
Shown with P8932-01 shade



P2061-0930K9  
Shown with P8934-01 shade

## OPTIONAL SHADE ACCESSORIES

Product No.	Screen Print	Description	Size
<b>P8932-01</b>	Fabric Linen	Accessory Shade	6-7/8" W., 6" ht. Extends 2-1/4".
<b>P8934-01</b>	Scroll	Accessory Shade	6-7/8" W., 6" ht. Extends 2-1/4".



# Balance

FROSTED WHITE ACRYLIC LENS AND A BRUSHED NICKEL FINISH ARE HIGHLIGHTS OF THESE ENERGY STAR FIXTURES. WALL OR CEILING MOUNTED. CAN BE INSTALLED VERTICALLY OR HORIZONTALLY.

### FEATURES

- 120v AC Replaceable LED module
- 623 source lumens, 69.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable with many ELV type dimmers
- Wall or ceiling mount
- Can be installed vertically or horizontally



P2094-0930K9

Product No.	Finish	Description	Size	Lamps *included
<b>P2091-0930K9</b>	Brushed Nickel	One-light bath	6" W., 5" ht. Extends 3". H/CTR 2-1/2".	*One 9w LED module
<b>P2092-0930K9</b>	Brushed Nickel	Two-light bath	11-1/2" W., 5" ht. Extends 3". H/CTR 2-1/2".	*Two 9w LED modules
<b>P2093-0930K9</b>	Brushed Nickel	Three-light bath	16-3/4" W., 5" ht. Extends 3". H/CTR 2-1/2".	*Three 9w LED modules
<b>P2094-0930K9</b>	Brushed Nickel	Four-Light Bath	22" W., 5" ht. Extends 3". H/CTR 2-1/2".	*Four 9w LED modules



P2091-0930K9



P2092-0930K9



P2093-0930K9

# Ace

MODERN WALL FIXTURES WITH GEOMETRIC FROSTED GLASS SHADES.

### FEATURES

- Sleek styling with etched glass
- Dimmable with many ELV type dimmers
- 120V AC Replaceable LED module
- 623 source lumens, 69.2 lumens per watt
- 3000K color temperature
- TM-21 60,000 hr. life
- 90+ CRI
- CA Title 24 Compliant



Product No.	Finish	Description	Size	Lamps *included
<b>P2142-1530K9</b> <b>P2142-2030K9</b>	Polished Chrome Antique Bronze	One-light with Etched Glass	7" W., 4-3/4" ht. Extends 4". H/CTR 2-3/4".	*One 9w LED module
<b>P2143-1530K9</b> <b>P2143-2030K9</b>	Polished Chrome Antique Bronze	Two-light with Etched Glass	15-1/2" W., 4-3/4" ht. Extends 4". H/CTR 2-3/8".	*Two 9w LED modules
<b>P2144-1530K9</b> <b>P2144-2030K9</b>	Polished Chrome Antique Bronze	Three-light with Etched Glass	24" W., 4-3/4" ht. Extends 4". H/CTR 2-3/8".	*Three 9w LED modules
<b>P2145-1530K9</b> <b>P2145-2030K9</b>	Polished Chrome Antique Bronze	Four-light with Etched Glass	32-1/2" W., 4-3/4" ht. Extends 4". H/CTR 2-3/8".	*Four 9w LED modules



P2142-1530K9



P2142-2030K9



P2143-2030K9



P2144-1530K9



P2145-2030K9

## Linear Fluorescent Bath

WHITE ACRYLIC DIFFUSER WITH BRUSHED NICKEL ENDS. CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

ADA 

Product No.	Finish	Description	Size	Lamps
<b>P7211-09EB</b>	Brushed Nickel	One-Light	25-5/8" W., 5-1/4" ht. Extends 4".	1-F17T8
<b>P7212-09EB</b>	Brushed Nickel	One-Light	37-5/8" W., 5-1/4" ht. Extends 4".	1-F17T8



P7212-09EB



P7211-09EB

## Contemporary Acrylic

BRUSHED NICKEL END CAPS FINISHED WITH TWIN LINEAR DETAILING. ACRYLIC DIFFUSER. WALL MOUNT. ENERGY STAR.



Product No.	Finish	Size	Ballast	Lamps
<b>P7227-09EB</b>	Brushed Nickel	25-1/2" L., 5-1/4" ht. Extends 4-1/2".	120V NPF electronic	2-F17T8
<b>P7228-09EB</b>	Brushed Nickel	37-1/4" L., 5-1/4" ht. Extends 4-1/2".	120V NPF electronic	2-F17T8
<b>P7229-09EB</b>	Brushed Nickel	49-1/4" L., 5-1/4" ht. Extends 4-1/2".	120V NPF electronic	2-F17T8



P7227-09EB



P7228-09EB



P7229-09EB

## Maier

Product No.	Finish	Description	Size	Lamps
<b>P7025-09EB</b>	Brushed Nickel w/white acrylic	Two-Light	30" W., 5" ht. Extends 5".	2 4-pin CFL, 2G11 base lamps 24w max.

CLEAN CYLINDER SILHOUETTES IN BRUSHED NICKEL WITH WHITE SATIN ACRYLIC SHADE. CAN BE INSTALLED HORIZONTALLY OR VERTICALLY. TITLE 24 COMPLIANT.

P7025-09EB



## Ribbed Linear Bath

WALL OR CEILING MOUNT. WHITE RIBBED ACRYLIC DIFFUSER. CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

ADA

Product No.	Finish	Description	Size	Lamps
<b>P7218-09EB</b>	Brushed Nickel	Two-Light	25" W., 6-1/2" ht. Extends 4".	2-F14T5
<b>P7221-09EB</b>	Brushed Nickel	Two-Light	49" W., 6-1/2" ht. Extends 4".	2-F17T8



P7218-09EB



P7221-09EB

## Metal Edge

SLEEK POLISHED CHROME METAL END CAPS.  
ACRYLIC DIFFUSER. WALL MOUNT ONLY.



Product No.	Finish	Size	Ballast	Lamps
<b>P7230-15EB</b>	Polished Chrome	24-1/2" L., 6" ht. Extends 4-1/4".	120/277V HPF electronic	2-F17T8
<b>P7231-15EB</b>	Polished Chrome	38-3/4" L., 6" ht. Extends 4-1/4"	120/277V HPF electronic	2-F17T8
<b>P7232-15EB</b>	Polished Chrome	48-1/2" L., 3-1/4" ht.. Extends 5-1/4"	120/277V HPF electronic	2-F17T8



P7230-15EB



P7231-15EB



P7232-15EB

## Soft Clouds

WHITE ACRYLIC DIFFUSERS CAN BE INSTALLED  
HORIZONTALLY OR VERTICALLY. PROVIDE LIGHT OUT  
AND DOWN. WALL MOUNT ONLY.



Product No.	Finish	Size	Ballast	Lamps
<b>P7114-60EB</b>	White	26-3/4" L., 6" ht. Extends 4-1/4".	120V HPF electronic	2-F17T8
<b>P7115-60EB</b>	White	38-3/4" L., 6" ht. Extends 4-1/4"	120V HPF electronic	2-F17T8
<b>P7116-60EB</b>	White	50-3/4" L., 6" ht. Extends 4-1/4"	120V HPF electronic	2-F17T8



P7114-60EB



P7115-60EB



P7116-60EB

## Linear Fluorescent Bath

WHITE ACRYLIC DIFFUSERS WITH BRUSH  
NICKEL ENDS. CAN BE INSTALLED  
HORIZONTALLY OR VERTICALLY.

ADA

Product No.	Finish	Description	Size	Lamps
<b>P7236-09</b>	Brushed Nickel	Two-Light	33-1/2" W., 4-3/8" ht. Extends 3-7/8".	2-F14T5
<b>P7237-09</b>	Brushed Nickel	Two-Light	45-1/4" W., 4" ht. Extends 3-7/8".	2-F17T8



P7236-09



P7237-09

# Bravo



P2004-09WB



P2006-09WB



P2005-09WB

Product No.	Finish	Description	Size	Lamps *included
<b>P2004-09WB</b>	Brushed Nickel	One-Light	7-1/4" W., 9" ht. Extends 8-3/4". H/CTR 4-1/2"	*1 13w GU24 CFL
<b>P2005-09WB</b>		Two-Light	17" W., 9" ht. Extends 8-3/4". H/CTR 6-1/8"	*2 13w GU24 CFL
<b>P2006-09WB</b>		Three-Light	26-3/4" W., 8-3/4" ht. Extends 8-3/4". H/CTR 6-3/8"	*3 13w GU24 CFL

# Gather



P2706-09EBWB



P2706-15EBWB



P2706-20EBWB

Product No.	Finish	Description	Size	Lamps *included
<b>P2706-09EBWB</b>	Brushed Nickel	One-Light	5" W., 7-1/2" ht. Extends 6-1/2". H/CTR 2-5/8"	*1 13w GU24 CFL
<b>P2706-15EBWB</b>	Polished Chrome			
<b>P2706-20EBWB</b>	Antique Bronze			
<b>P2707-09EBWB</b>	Brushed Nickel	Two-Light	12" W., 7-1/2" ht. Extends 6-1/2". H/CTR 2-1/2"	*2 13w GU24 CFL
<b>P2707-15EBWB</b>	Polished Chrome			
<b>P2707-20EBWB</b>	Antique Bronze			
<b>P2708-09EBWB</b>	Brushed Nickel	Three-Light	24" W., 7-1/2" ht. Extends 6-1/2". H/CTR 2-1/2"	*3 13w GU24 CFL
<b>P2708-15EBWB</b>	Polished Chrome			
<b>P2708-20EBWB</b>	Antique Bronze			
<b>P2709-09EBWB</b>	Brushed Nickel	Four-Light	30" W., 7-1/2" ht. Extends 6-1/2". H/CTR 2-1/2"	*4 13w GU24 CFL
<b>P2709-15EBWB</b>	Polished Chrome			
<b>P2709-20EBWB</b>	Antique Bronze			



P2707-20EBWB



P2708-20EBWB



P2707-09EBWB



P2707-15EBWB



P2709-09EBWB



P2709-15EBWB



P2708-15EBWB



## Hanging

Add personality and functional illumination to spaces with hanging fixtures, such as chandeliers and pendants. These decorative light fixtures are great for small spaces or unexpected areas, such as hallways or utility rooms, as well as popular applications, including kitchens, bath and foyer areas.





FEATURES

- 120V AC Replaceable LED module
- 623 source lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

# Prismatic Glass

Product No.	Finish	Description	Size	Lamp *included
<b>P5075-0930K9</b>	Brushed Nickel	One-light mini-pendant with clear prismatic glass and etched diffuser	9-1/8-" dia., 8-1/2" ht. Overall ht. w/ stem 74".	*1 9w LED module
<b>P5143-0930K9</b>		One-light pendant with clear prismatic glass and etched diffuser	12-3/4" dia., 10-7/8" ht. Overall ht. w/stem 77".	
<b>P4715-0930K9</b>		Three-light LED linear chandelier	9-1/8" dia., 12-5/8" ht. Overall ht. w/stem xx".	*3 9w LED module



P5075-0930K9



P5143-0930K9



P4715-0930K9



# Retro

Retro style LED pendant with prismatic glass

Product No.	Finish	Description	Size	Lamp *included
<b>P5053-0930K9</b>	Brushed Nickel	One-light	14-5/8-" dia., 6-5/8" ht. Overall ht. w/stem 73"; wire 15'.	*1 17w LED module
<b>P5053-1530K9</b>	Polished Chrome			
<b>P5053-7430K9</b>	Venetian Bronze			



FEATURES

- 120V AC Replaceable LED module
- 1211 source lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



P5053-0930K9



P5053-1530K9



P5053-7430K9

P5175-0930K9

P5175-3030K9

P5175-7930K9

P5175-2030K9



THIS UNIQUELY SHAPED PENDANT HAS A BRUSHED NICKEL FINISH WITH A WHITE LINEN INTERIOR FOR OPTIMAL LIGHT OUTPUT.

## Pure



Product No.	Finish	Description	Size	Lamps *included
<b>P5175-0930K9</b>	Brushed Nickel	Cord hung LED Pendant	6-1/2" dia., 8-7/8" ht. Overall ht. w/cord 130"; wire 10'.	*1 9w LED module
<b>P5175-2030K9</b>	Antique Bronze			
<b>P5175-3030K9</b>	White			
<b>P5175-7930K9</b>	Pistachio			



P5176-0930K9

P5176-2030K9

## Simple



Product No.	Finish	Description	Size	Lamps *included
<b>P5176-0930K9</b>	Brushed Nickel	Cord hung LED Pendant	5-7/8" dia., 8-5/8" ht. Overall ht. w/cord 130"; wire 10'	*1 9w LED module
<b>P5176-2030K9</b>	Antique Bronze			

P5186-0930K9

P5187-0930K9



## Kiss

THIS UNIQUELY SHAPED PENDANT HAS A BRUSHED NICKEL FINISH WITH A WHITE LINEN INTERIOR FOR OPTIMAL LIGHT OUTPUT.



Product No.	Finish	Description	Size	Lamps *included
<b>P5186-0930K9</b>	Brushed Nickel	One-light mini-pendant	5" dia., 5-7/8" ht. Overall ht. w/stem 72"	*1 9w LED module
<b>P5187-0930K9</b>	Brushed Nickel	One-light pendant	10" dia., 10-3/4" ht. Overall ht. w/stem 77"	*1 17w LED module



FEATURES

- Inspired by vintage light fixtures found in early 20th century train stations.
- 120V AC Replaceable LED module
- 17w: 1211source lumens, 71.2 lumens per watt
- 9w: 623 lumens, 69.2 lumens per watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



Brookside



Product No.	Finish	Description	Size	Lamps *included
<b>P5023-0930K9</b>	Brushed Nickel	One-light mini-pendant	8" dia., 7-1/2" ht. Overall ht. w/stem 64"; wire 10'.	*1 17w LED module
<b>P5023-2030K9</b>	Antique Bronze			
<b>P5024-0930K9</b>	Brushed Nickel	One-light	12" dia., 9-1/8" ht. Overall ht. w/stem 65"; wire 15'.	
<b>P5024-2030K9</b>	Antique Bronze			



FEATURES

- Industrial roots in form and function.
- 120V AC Replaceable LED module
- 17w: 1211 source lumens, 71.2 lumens per watt
- 9w: 623 source lumens, 69.2 lumens per watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

Fresnel Lens



Product No.	Finish	Description	Size	Lamps *included
<b>P5197-0930K9</b>	Brushed Nickel	One-light	16" dia., 13-1/4" ht. Overall ht. w/stem 79"; wire 10'.	*1 17w LED module
<b>P5197-10830K9</b>	Oil Rubbed Bronze			

District

FEATURES

- 120V AC Replaceable LED module
- 623 source lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



Product No.	Finish	Description	Size	Lamp *included
<b>P5551-2030K9</b>	Antique Bronze	Large Hanging Lantern	12" dia., 8-1/4" ht. Overall ht. w/ cord 130" wire 12'.	*One 9w LED module
<b>P5551-8230K9</b>	Metallic Gray			
<b>P5535-2030K9</b>	Antique Bronze	Medium Hanging Lantern	8" dia., 6-1/4" ht. Overall ht. w/ cord 130" wire 12'.	*One 9w LED module
<b>P5535-8230K9</b>	Metallic Gray			
<b>P5623-2030K9</b>	Antique Bronze	Large Hanging Lantern	12" dia., 10-1/2" ht. Extends 13-1/4". H/CTR 5".	*One 9w LED module
<b>P5623-8230K9</b>	Metallic Gray			

# Warehouse

CORD HUNG METAL SHADE WITH WHITE INNER-LINING

### FEATURES

- 120V AC Replaceable LED module
- 1211 source lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



Product No.	Finish	Description	Size	Lamp *included
<b>P5087-0930K9</b>	Brushed Nickel	One-light mini-pendant	10-1/8-" dia., 6-1/2" ht. Cord 10'.	
<b>P5094-0930K9</b>	Brushed Nickel	One light	16" dia., 7-1/2" ht. Overall ht. w/cord 129"; Cord 10'.	*1 17w LED module
<b>P5094-3030K9</b>	White			
<b>P5094-4530K9</b>	Dark Green			
<b>P5094-7430K9</b>	Venetian Bronze			

P5094-0930K9



P5087-0930K9



P5087-3030K9



P5087-4530K9



P5087-7430K9



# Markor

CREATED WITH MID-CENTURY  
DESIGNS IN MIND. ADD A SPLASH  
OF VINTAGE MODERN FLAIR WITH  
A VARIETY OF FABRICS, SHADE  
SIZES AND PENDANT KITS

## 22" DRUM SHADES

Acrylic bottom diffuser.

For use with P5198 or P5199.

Size: 22" dia., 10" ht.

- P8768-01** Chloe Floral Fabric
- P8824-01** Black Parchment Paper
- P8825-01** Beige Silken Fabric
- P8830-30** Summer Linen
- P8830-39** Crimson
- P8830-56** Khaki
- P8830-59** Harvest Linen

## 10" DRUM SHADES

Acrylic bottom diffuser.

For use with P5198 only.

Size: 10" dia., 8" ht.

- P8820-01** Black Parchment Paper with White Liner
- P8821-01** Beige Silken Fabric
- P8828-30** Summer Linen
- P8828-39** Crimson
- P8828-56** Khaki
- P8828-59** Harvest Linen

## 9" DRUM SHADE

Acrylic bottom diffuser.

Size: 9" dia., 8" ht.

- P8928-01** Chiffon Ribbon Fabric







**P8829-30**  
shown with pendant kit  
(sold separately)



**P8829-39**  
shown with pendant kit  
(sold separately)



**P8829-56**  
shown with pendant kit  
(sold separately)



**P8929-01**  
shown with pendant kit  
(sold separately)



**P8829-59**  
shown with pendant kit  
(sold separately)



**P8830-59**  
shown with pendant kit  
(sold separately)

**16" DRUM SHADE**  
Acrylic bottom diffuser.  
For use with P5198 or P5199.  
Size: 16" dia., 10" ht.  
**P8766-01** Chloe Floral Fabric  
**P8822-01** Black Parchment Paper  
with White Liner  
**P8823-01** Beige Silken Fabric  
**P8929-01** Chiffon Ribbon Fabric  
**P8829-30** Summer Linen  
**P8829-39** Crimson  
**P8829-56** Khaki  
**P8829-59** Harvest Linen



**P5198-0930K9**

**ONE-LIGHT LED PENDANT KIT**  
**P5198-0930K9** Brushed Nickel  
**P5198-2030K9** Antique Bronze  
One-light pendant kit for all Markor shades. 3000K. 90+ CRI. 1211 lumens.  
Size: 5-3/4" dia., 5-3/8" ht. Overall ht. w/stem and lamps 62"; wire 10'.  
Lamp: One 17w LED module included.



Stems include two 6", one 12" and two 15" stems with 90° swivel.

# Wisten



Product No.	Finish	Description	Size	Lamp *included
<b>P5108-09EBWB</b> <b>P5108-20EBWB</b>	Brushed Nickel Antique Bronze	One-light with tripled etched glass	4" dia., 6-3/4" ht. Overall ht. w/ stem 120" wire 15'.	*1 13w GU24 CFL

P5108-09EBWB



P5108-20EBWB




# Avalon



Product No.	Finish	Description	Size	Lamp *included
<b>P5145-09EBWB</b> <b>P5145-20EBWB</b>	Brushed Nickel Antique Bronze	One-light with etched alabaster glass	7-3/4" dia., 6-1/2" ht. Overall ht. w/ stem 63" wire 10'.	*1 13w GU24 CFL

P5145-20EBWB



P5145-09EBWB



# Bravo



Product No.	Finish	Description	Size	Lamp *included
<b>P5300-09EBWB</b>	Brushed Nickel	One-light with etched glass	7-1/4" dia., 6-1/2" ht. Overall ht. w/ stem 94" wire 10'.	*1 13w GU24 CFL



P5300-09EBWB



P5095-09EBWB



P5095-20EBWB

P5096-09EBWB



P5096-20EBWB



# Trinity



Product No.	Finish	Description	Size	Lamp *included
<b>P5095-09EBWB</b> <b>P5095-20EBWB</b>	Brushed Nickel Antique Bronze	One-light pendant with etched glass	18" dia., 9-1/2" ht. Overall ht. w/ chain 85" wire 15'.	*1 13w GU24 CFL
<b>P5096-09EBWB</b> <b>P5096-20EBWB</b>	Brushed Nickel Antique Bronze	One-light mini-pendant with etched glass	6-1/2" dia., 7" ht. Overall ht. w/ stem 64" wire 10'.	

# Eclipse



Product No.	Finish	Description	Size	Lamp *included
<b>P7322-09EBWB</b>	Brushed Nickel	Three-light pendant with opal glass	19-3/8" dia., 17" ht. Overall ht. w/ chain 56" wire 15'.	*3 26w 4-pin Quad CFL. G24q-3 base.
<b>P7322-20EBWB</b>	Antique Bronze			
<b>P7323-09EBWB</b>	Brushed Nickel	Four-light pendant with opal glass	27-3/8" dia., 24-1/8" ht. Overall ht. w/ chain 63" wire 15'.	*4 26w 4-pin Quad CFL. G24q-3 base.
<b>P7323-20EBWB</b>	Antique Bronze			

# Avalon



Product No.	Finish	Description	Size	Lamp *included
<b>P4276-09EBWB</b>	Brushed Nickel	Three-light chandelier with alabaster glass	24-3/8" dia., 15-5/8" ht. Overall ht. w/ chain 91"; wire 15'.	*3 13w GU24 CFL
<b>P5145-09EBWB</b>	Brushed Nickel	Mini-pendant with alabaster glass	7-3/4" dia., 6-1/4" ht. Overall ht. w/ stem 63"; wire 15'.	*1 13w GU24 CFL
<b>P5145-20EBWB</b>	Antique Bronze			
<b>P4275-09EBWB</b>	Brushed Nickel	Five-light chandelier with alabaster glass	26-1/2" dia., 22-5/8" ht. Overall ht. w/ chain 98"; wire 15'.	*5 13w GU24 CFL
<b>P3468-09EBWB</b>	Brushed Nickel	Two-light Foyer with alabaster glass	13-1/8" dia., 15" ht. Overall ht. w/ chain 90"; wire 15'.	*2 13w GU24 CFL



P4365-09EBWB



P4328-20EBWB



P3474-09EBWB



P4329-20EBWB



# Trinity

ETCHED GLASS



Product No.	Finish	Description	Size	Lamp *included
<b>P4365-09EBWB</b> <b>P4365-20EBWB</b>	Brushed Nickel Antique Bronze	Fifteen-light chandelier	43-3/4" dia., 43-5/8" ht. Overall ht. w/ chain 167"; wire 15'.	*15 13w GU24 CFL
<b>P4329-09EBWB</b> <b>P4329-20EBWB</b>	Brushed Nickel Antique Bronze	Nine-light chandelier	30" dia., 33" ht. Overall ht. w/ stem 156"; wire 15'.	*9 13w GU24 CFL
<b>P4328-09EBWB</b> <b>P4328-20EBWB</b>	Brushed Nickel Antique Bronze	Five-light chandelier	23" dia., 24" ht. Overall ht. w/ chain 99"; wire 15'.	*5 13w GU24 CFL
<b>P4324-09EBWB</b> <b>P4324-20EBWB</b>	Brushed Nickel Antique Bronze	Three-light chandelier	19" dia., 20" ht. Overall ht. w/ chain 95"; wire 15'.	*3 13w GU24 CFL

Product No.	Finish	Description	Size	Lamp *included
<b>P3474-09EBWB</b> <b>P3474-20EBWB</b>	Brushed Nickel Antique Bronze	Three-light Foyer	18" dia., 24" ht. Overall ht. w/ chain 99"; wire 15'.	*3 13w GU24 CFL

Product No.	Finish	Description	Size	Lamp *included
<b>P5096-09EBWB</b> <b>P5096-20EBWB</b>	Brushed Nickel Antique Bronze	Mini Pendant	6-12" dia., 7" ht. Overall ht. w/ chain 64"; wire 10'.	*1 13w GU24 CFL

P5096-09EBWB



P5096-20EBWB





# Bravo

ETCHED GLASS



Product No.	Finish	Description	Size	Lamp *included
<b>P3912-09WB</b>	Brushed Nickel	Three-light foyer	21" dia., 23-1/2" ht. Overall ht. w/ chain 98"; wire 180'.	*3 13w GU24 CFL
<b>P4621-09WB</b>	Brushed Nickel	Three-light chandelier	23" dia., 20-1/8" ht. Overall ht. w/ stem 95"; wire 12'.	*3 13w GU24 CFL
<b>P4623-09WB</b>	Brushed Nickel	Five-light chandelier	27" dia., 23" ht. Overall ht. w/ chain 97"; wire 12'.	*5 13w GU24 CFL
<b>P5300-09WB</b>	Brushed Nickel	One-light mini-pendant	7-1/4" dia., 6-1/2" ht. Overall ht. w/ chain or stem 94"; wire 10'.	*1 13w GU24 CFL





P4627-20EBWB



P4441-09EBWB



P4440-20EBWB



## Gather

SIMPLIFIED FRAME WITH UPDATED STYLING AND ELEGANT ETCHED GLASS SHADES. AVAILABLE IN ENERGY STAR VERSIONS.



P5113-09EBWB



P5113-20EBWB




Product No.	Finish	Description	Size	Lamps *included
<b>P4627-09EBWB</b> <b>P4627-20EBWB</b>	Brushed Nickel Antique Bronze	Two-tier. Nine-light chandelier	27-3/4" dia., 20-1/2" ht. Overall ht. w/ chain 84"; wire 120".	*9 13w GU24 CFL
<b>P4441-09EBWB</b> <b>P4441-20EBWB</b>	Brushed Nickel Antique Bronze	Five-light chandelier	20-1/2" dia., 15" ht. Overall ht. w/ chain 60"; wire 96".	*5 13w GU24 CFL
<b>P4440-09EBWB</b> <b>P4440-20EBWB</b>	Brushed Nickel Antique Bronze	Three-light chandelier	18-1/2" dia., 15" ht. Overall ht. w/ chain 60"; wire 96".	*3 13w GU24 CFL
Product No.	Finish	Description	Size	Lamps *included
<b>P5113-09EBWB</b> <b>P5113-20EBWB</b>	Brushed Nickel Antique Bronze	Chain or stem hung mini-pendant	4" dia., 5-3/4" ht. Overall ht. w/ chain/ stem 63"; wire 96".	*1 13w GU24 CFL



## Undercabinet

Designed to fit in small spaces and provide accent or task lighting, Progress Lighting's undercabinet offering features a subtle – yet wide distribution – under kitchen cabinets, on bookshelves, in display cases, alcoves and more.



# HIDE·a·Lite<sup>3</sup>

## 120V LED Strips | Undercabinet Systems

Direct Wire and Linkable,  
with long-life LED's

### Electrical

Each fixture includes 120V dimmable electronic power supplies rated for long-life continuous use. An on/off rocker switch is included.

### Lamping

70% lumen maintenance over 35,000 hours. 3000K, 80+ CRI.

### Construction

Extruded aluminum frame, polycarbonate end plates match frame finish. Tempered micro-prismatic glass lens.

### Linkable

The system can be powered from a single location using the P8740 direct-wire junction box (each fixture can also be direct-wired individually). Using the HAL3 linking cable accessories (P8733-P8743), the fixtures can be linked together to form a continuous row of illumination. (Note: The linking cables can be used with or without the use of the P8740 junction box).

### Dimming

Smooth and continuous dimming on many incandescent dimmer switches (Note: Reference manufacturers' minimum load requirements for dimmer switches). (Except P7002)



Side view showing cable connector

Product No.	Finish	Description	Size	Lamps	Lumens
<b>P7002-20</b>	Bronze	120V LED undercabinet (Non-dimmable)	3-1/2" W., 9" L., Extends 1".	4w LED.	157
<b>P7002-30</b>	White				



P7002-20



P7002-30

Product No.	Finish	Description	Size	Lamps	Lumens
<b>P7012-20</b>	Bronze	120V LED undercabinet	3-1/2" W., 12" L., Extends 1".	8w LED	284
<b>P7012-30</b>	White				



P7012-20



P7012-30

Product No.	Finish	Description	Size	Lamps	Lumens
<b>P7005-20</b>	Bronze	120V LED undercabinet	3-1/2" W., 18" L., Extends 1".	10w LED	425
<b>P7005-30</b>	White				



P7005-20

Product No.	Finish	Description	Size	Lamps	Lumens
<b>P7013-20</b>	Bronze	120V LED undercabinet	3-1/2" W., 24" L., Extends 1".	14w LED	555
<b>P7013-30</b>	White				



P7013-30

# 120V AC LED Puck

## Electrical

120V AC linkable LED puck. Wet location listed.

## Construction

Die cast enclosure. V5 rated cover and frosted lens.

## Dimmable

Smooth and continuous dimming using most incandescent dimmers (Note: Reference dimmer manufacturer's minimum load requirements.)

## Lamping

Long life LED's 50,000 hours, 70% lumen maintenance. 3000K color temperature, 85+ CRI.

## Linkable


This system can be powered from a single location using the P8740 direct-wire junction box using HAL3 linking cables (P8733, P8735, P8737, P8738). The fixtures can be linked together to form a continuous row of illumination.

Product No.	<b>P7510-30</b> White
Description	Two-light LED Puck, 120V LED puck.
Size	3-1/4" dia., 15/16" ht.
Lamps	4w LED array.
Lumens	274 lumen output, 62 lumens per watt

P7510-30




Quick connect locations on two sides and the top.



## HAL 3 JUNCTION BOX

Product No.	<b>P8740-20</b> Antique Bronze <b>P8740-30</b> White
Description	HAL3 junction box.
Size	3-1/4" W., 7/8" ht. 3-1/2" L.

P8740-30



Shown P8740-30 with P8737-30

## HAL 3 LINKING CABLES

Product No.	<b>P8733-20</b> Antique Bronze <b>P8733-30</b> White
Description	12" Undercabinet fixture linking cable.
Size	3/4" W., 3/8" ht. 12" L.

P8733-30



Product No.	<b>P8735-20</b> Antique Bronze <b>P8735-30</b> White
Description	6" Undercabinet fixture linking cable.
Size	3/4" W., 3/8" ht. 6" L.

P8735-20




Product No.	<b>P8737-20</b> Antique Bronze <b>P8737-30</b> White
Description	18" Undercabinet fixture linking cable.
Size	3/4" W., 3/8" ht. 18"L.

P8737-30



Product No.	<b>P8738-20</b> Antique Bronze <b>P8738-30</b> White
Description	24" Undercabinet fixture linking cable.
Size	3/4" W., 3/8" ht. 24" L.

P8738-30


































Product No.	<b>P8743-20</b> Antique Bronze <b>P8743-30</b> White
Description	Coupling cable, Connects two linking cables together.
Size	3/4" W., 1/2" ht. 6" L.

P8743-20



# CEILING HEIGHT CROSSOVER

Ceiling Height	Legacy Lamps	Pro -Optic PREMIER		Pro -Optic	Mini Flush Mount	Recessed
20-30'	 <p>100W MH 250W T4 70W CFL</p>	<p>8" Housing &amp; Trim</p>  <p>P8215-EBG4 P8220-EBG4</p>  <p>P8120</p>	<p>6" Housing &amp; Trim</p>  <p>P8212-EBG4 P8214-EBG4</p>  <p>P8112</p>			
10-20'	 <p>42/57W CFL Twin 26W CFL</p>	<p>8" Housing &amp; Trim</p>  <p>P8103-EBG4 P8102-EBG4</p>  <p>P8133</p>	<p>6" Housing &amp; Trim</p>  <p>P8002-EBG4 P8023-EBG4</p>  <p>P8050</p>			
		<p>4" Housing &amp; Trim</p>  <p>P8064-EBG4</p>  <p>P8206</p>				
10-15'	 <p>26/32W CFL</p>	<p>8" Housing &amp; Trim</p>  <p>P8103-EBG4 P8102-EBG4</p>  <p>P8133</p>	<p>6" Housing &amp; Trim</p>  <p>P8002-EBG4 P8023-EBG4</p>  <p>P8050</p>	<p>8" Housing &amp; Trim</p>  <p>P8216-EBG4</p>  <p>P8104</p>	<p>7"</p>  <p>P8022</p>  <p>P8027</p>  <p>P8222</p>	<p>6"</p>  <p>P8071-28/30K9-L10-STR2</p>  <p>P8071-28/35K9-L10-STR2</p>
8-10'	 <p>18W CFL 75W INC 65W INC</p>				<p>5"</p>  <p>P8240</p>  <p>P8241</p>  <p>P8247</p>	<p>6"</p>  <p>P8071-28/30K9-L10-STR2</p>  <p>P8061</p>  <p>P8080</p>





## Recessed

Designed to fit in small spaces and provide accent or task lighting, Progress Lighting's undercabinet offering features a subtle – yet wide distribution – under kitchen cabinets, on bookshelves, in display cases, alcoves and more.





6"

6" NEW CONSTRUCTION HOUSING

Product No.	<b>P87-LED</b>
Description	New Construction Air-Tight IC and Non-IC. Integral quick connect mates with P8071 series LED trims.
Ceiling opening	6-7/8" dia.
Plaster frame	7-7/8" x 10-3/4"
Recessed depth	7-1/2"
Pryouts	1/2" & 3/4"

P87-LED



6" NEW CONSTRUCTION or REMODEL TRIMS

Product No.	<b>P8071-20/30K9-AC1-L07</b> Antique Bronze
	<b>P8071-28/30K9-AC1-L07</b> White
	<b>P8071-31/30K9-AC1-L07</b> Black
	<b>P8071-82/30K9-AC1-L07</b> Metallic Gray

Description 700 lumen 3000K



Includes Edison base socket and Quick-Link connector

P8071-20/30K9-AC1-L07



P8071-28/30K9-AC1-L07



P8071-31/30K9-AC1-L07



P8071-82/30K9-AC1-L07



FEATURES

- Frosted polycarbonate lens controls direct glare from the LEDs
- Dimmable with many ELV type dimmers
- 12-watt input power
- Lumen output 700 lumens
- Lumen output and distribution comparable to a 65w BR30 incandescent lamp
- 3000K color temperature
- 90+ CRI
- TM-21 60,000 hours life
- Suitable for use in IC or NON-IC applications
- CSAus listed for wet locations

Product No.	<b>P8071-28/30K-L10-STR2</b> White
-------------	------------------------------------

Description 1000 lumen 3000K

Product No.	<b>P8071-28/35K-L10-STR2</b> White
-------------	------------------------------------

Description 1000 lumen 3500K



Includes Edison base socket and Quick-Link connector

P8071-28/30K-L10 STR2



P8071-28/35K-L10 STR2



FEATURES

- Frosted polycarbonate lens controls direct glare from the LEDs
- Dimmable with many ELV type dimmers
- 12-watt input power
- Lumen output 1037 lumens
- Lumen output and distribution comparable to a 75w PAR30 incandescent lamp
- 80+ CRI
- TM-21 60,000 hours life
- Suitable for use in IC or NON-IC applications
- Available in 3000K and 3500K color temperatures
- cULus listed for wet locations

# 4" & 5"

## 4" NEW CONSTRUCTION or REMODEL HOUSING

Product No.	<b>P831-LED</b>
Description	New Construction Air-Tight, IC and Non-IC. Integral quick connect mates with P8080 series LED trims.
Ceiling opening	4-1/2"
Plaster frame	8-3/8" x 13"
Recessed depth	7-1/2"



Product No.	<b>P830-LED</b>
Description	New Construction Non-IC. Integral quick connect mates with P8080 series LED trims
Ceiling opening	4-1/2"
Plaster frame	7-7/8" x 10-3/4"
Recessed depth	5-1/2"
Pryouts	1/2" and 3/4"



Product No.	<b>P832-LED</b>
Description	Remodel Non-IC. Retrofit version of P830-TG for use in existing ceilings
Ceiling opening	4-1/4"
Recessed depth	5-1/2"
Pryouts	1/2"





## 4" NEW CONSTRUCTION or REMODEL TRIMS

Product No.	<b>P8080-20/30K9-AC1-L06</b> Antique Bronze <b>P8080-28/30K9-AC1-L06</b> White <b>P8080-31/30K9-AC1-L06</b> Black <b>P8080-82/30K9-AC1-L06</b> Metallic Gray
Description	600 lumen 3000K



Includes Edison base socket and Quick-Link connector





- FEATURES**
- LED (Light Emitting Diode) lamp included
  - 10-watt input power
  - Lumen output 620 lumens
  - Lumen output and distribution comparable to 50w R20 incandescent lamp
  - 90+ CRI
  - TM-21 60,000 hours life
  - Suitable for use in IC or NON-IC applications
  - cULus listed for wet locations

## 5" P8061 NEW CONSTRUCTION or REMODEL (TRIMS ONLY)

Product No.	<b>P8061-20/30K9-AC1-L06</b> Antique Bronze <b>P8061-28/30K9-AC1-L06</b> White <b>P8061-31/30K9-AC1-L06</b> Black <b>P8061-82/30K9-AC1-L06</b> Metallic Gray
Description	600 lumen 3000K



Includes Edison base socket and Quick-Link connector



- FEATURES**
- LED (Light Emitting Diode) lamp included
  - Dimmable with many ELV type dimmers
  - 12-watt input power
  - Lumen output 635 lumens
  - Lumen output and distribution comparable to 65w BR30 incandescent lamp
  - 90+ CRI
  - TM-21 60,000 hours life
  - Suitable for use in IC or NON-IC applications
  - cULus listed for wet locations

# 2" Pro-Optic®

## 2" NEW CONSTRUCTION HOUSING & TRIM

Ceiling Opening	2-7/8"
Ceiling Thickness	1/2" - 1-1/4"
Pryouts	1/2"



**P8152-21A/27K9**  
Clear Alzak®



**P8152-28/27K9**  
White



### FEATURES

- 120V high efficiency driver
- 2700K
- TM-21 50,000 hour life
- 900 lumens
- 21 watts
- 35° distribution
- 95+ CRI
- Suitable for wet locations, non-IC rated
- Forward phase dimmable to 10%
- 5 year warranty
- Completely accessible from below the ceiling

## ACCESSORY FOR 2"

Product No.	<b>P8556-01</b>
Description	IC Box with bar hangers.



## WALL WASH

**P8153-21A/27K9**  
Clear Alzak®



**P8153-28/27K9**  
White



# 4" Pro-Optic®

## 4" NEW CONSTRUCTION HOUSING

Product No.	<b>P8064-EBG4</b>
Ceiling Opening	5-3/8"
Ceiling Thickness	1-1/4"
Plaster Frame	9-1/16" x 15-1/2"
Pryouts	1/2" and 3/4"



## 1100 LUMEN OPEN MODULE TRIMS FOR P8064

**P8067-21A/30KG4**  
**P8067-21A/35KG4**  
**P8067-21A/40KG4**  
Clear Alzak®



**P8067-22A/30KG4**  
**P8067-22A/35KG4**  
**P8067-22A/40KG4**  
Gold Alzak®




**P8067-28/30KG4**  
**P8067-28/35KG4**  
**P8067-28/40KG4**  
White



### FEATURES

- Universal 120-277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers included
- Suitable for wet locations, non-IC rated
- 5 year warranty

P8064-EBG4



## 2000 LUMEN OPEN MODULE TRIMS FOR P8064

**P8206-21A/30KG4**  
**P8206-21A/35KG4**  
**P8206-21A/40KG4**  
Clear Alzak®



**P8206-22A/30KG4**  
**P8206-22A/35KG4**  
**P8206-22A/40KG4**  
Gold Alzak®



**P8206-28/30KG4**  
**P8206-28/35KG4**  
**P8206-28/40KG4**  
White



# 6" Pro-Optic®

## 6" NEW CONSTRUCTION HOUSING

Product No. **P8216-EB**  
**P8216-DM**  
**P8216-277EB**  
**P8216-277DM**



Ceiling Opening 6-1/4"

Ceiling Thickness 1-1/4"

Plaster Frame 9-1/8" x 14"

Pryouts 1/2" and 3/4"

Note Built to order with a 2-4 week lead time

P8216-EB  
 P8216-DM  
 P8216-277EB  
 P8216-277DM



## 900 LUMEN OPEN MODULE TRIMS FOR P8216

**P8104-28/30K**  
**P8104-28/35K**  
**P8104-28/40K**  
 White



## 1300 LUMEN OPEN MODULE TRIMS FOR P8216

**P8105-28/30K**  
**P8105-28/35K**  
**P8105-28/40K**  
 White



## 1500 LUMEN OPEN MODULE TRIMS FOR P8216


**P8106-28/30K**  
**P8106-28/35K**  
**P8106-28/40K**  
 White






# 8" Pro-Optic<sup>®</sup>

## 8" NEW CONSTRUCTION HOUSING

Product No.	<b>P8220-EB120VG4</b> <b>P8220-EB277VG4</b>	
Ceiling Opening	6-1/4"	
Ceiling Thickness	1-1/4"	
Plaster Frame	9-1/16" x 15-1/2"	
Pryouts	1/2" and 3/4"	

P8220-EB120VG4  
P8220-EB277VG4



## 3000 LUMEN OPEN MODULE TRIMS FOR P8220


<b>P8120-21A/30KG4</b> <b>P8120-21A/35KG4</b> <b>P8120-21A/40KG4</b> Clear Alzak <sup>®</sup>	<b>P8120-22A/30KG4</b> <b>P8120-22A/35KG4</b> <b>P8120-22A/40KG4</b> Gold Alzak <sup>®</sup>	<b>P8120-28/30KG4</b> <b>P8120-28/35KG4</b> <b>P8120-28/40KG4</b> White
--	---	--




### FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers incl.
- Suitable for wet locations, non-IC rated
- 5 year warranty

## 8" NEW CONSTRUCTION HOUSING

Product No.	<b>P8103-EBG4</b>	
Ceiling Opening	6-1/4"	
Ceiling Thickness	1-1/4"	
Plaster Frame	9-1/16" x 15-1/2"	
Pryouts	1/2" and 3/4"	

P8103-EBG4



## 1100 LUMEN OPEN MODULE TRIMS FOR P8103

<b>P8121-21A/30KG4</b> <b>P8121-21A/35KG4</b> <b>P8121-21A/40KG4</b> Clear Alzak <sup>®</sup>	<b>P8121-22A/30KG4</b> <b>P8121-22A/35KG4</b> <b>P8121-22A/40KG4</b> Gold Alzak <sup>®</sup>	<b>P8121-28/30KG4</b> <b>P8121-28/35KG4</b> <b>P8121-28/40KG4</b> White
--	---	--



### FEATURES

- 120V or 277V high efficiency driver
- Remote phosphor technology for controlled color consistency
- 3000K, 3500K and 4000K options
- 80+ CRI
- 50 lumens per watt fixture efficacy
- TM-21 50,000 hour life
- J-box rated for (8) #12 90° conductors (4 in/4 out)
- Light commercial bar hangers incl.
- Suitable for wet locations, non-IC rated
- 5 year warranty



## 2000 LUMEN OPEN MODULE TRIMS FOR P8103

<b>P8133-21A/30KG4</b> <b>P8133-21A/35KG4</b> <b>P8133-21A/40KG4</b> Clear Alzak <sup>®</sup>	<b>P8133-22A/30KG4</b> <b>P8133-22A/35KG4</b> <b>P8133-22A/40KG4</b> Gold Alzak <sup>®</sup>	<b>P8133-28/30KG4</b> <b>P8133-28/35KG4</b> <b>P8133-28/40KG4</b> White
--	---	--



# 8" Pro-Optic<sup>®</sup>

## 8" RETROFIT HOUSING

Product No.	<b>P8102-EBG4</b>	
Ceiling Opening	min. 8-1/8" max. 8-3/4"	
Product No.	<b>P8102-EBSDG4</b>	
<b>(Must use WF trims)</b>		
Ceiling Opening	min. 7-15/16" max. 8-1/8"	
Ceiling Thickness	1-1/2"	
Plaster Frame	9" x 13-3/4" to 16"	
Pryouts	1/2" and 3/4"	

P8102-EBG4  
P8102-EBSDG4



## 1100 LUMEN OPEN MODULE TRIMS FOR P8102-EB

<b>P8121-21A/30KG4</b>	<b>P8121-22A/30KG4</b>	<b>P8121-28/30KG4</b>
<b>P8121-21A/35KG4</b>	<b>P8121-22A/35KG4</b>	<b>P8121-28/35KG4</b>
<b>P8121-21A/40KG4</b>	<b>P8121-22A/40KG4</b>	<b>P8121-28/40KG4</b>
Clear Alzak <sup>®</sup>	Gold Alzak <sup>®</sup>	White

## 1100 LUMEN OPEN MODULE TRIMS FOR P8102-EBSD

<b>P8121-21A/30KWFG4</b>	<b>P8121-22A/30KWFG4</b>	<b>P8121-28/30KWFG4</b>
<b>P8121-21A/35KWFG4</b>	<b>P8121-22A/35KWFG4</b>	<b>P8121-28/35KWFG4</b>
<b>P8121-21A/40KWFG4</b>	<b>P8121-22A/40KWFG4</b>	<b>P8121-28/40KWFG4</b>
Clear Alzak <sup>®</sup>	Gold Alzak <sup>®</sup>	White



## 2000 LUMEN OPEN MODULE TRIMS FOR P8102-EB

<b>P8133-21A/30KG4</b>	<b>P8133-22A/30KG4</b>	<b>P8133-28/30KG4</b>
<b>P8133-21A/35KG4</b>	<b>P8133-22A/35KG4</b>	<b>P8133-28/35KG4</b>
<b>P8133-21A/40KG4</b>	<b>P8133-22A/40KG4</b>	<b>P8133-28/40KG4</b>
Clear Alzak <sup>®</sup>	Gold Alzak <sup>®</sup>	White

## 2000 LUMEN OPEN MODULE TRIMS FOR P8102-EBSD

<b>P8133-21A/30KWFG4</b>	<b>P8133-22A/30KWFG4</b>	<b>P8133-28/30KWFG4</b>
<b>P8133-21A/35KWFG4</b>	<b>P8133-22A/35KWFG4</b>	<b>P8133-28/35KWFG4</b>
<b>P8133-21A/40KWFG4</b>	<b>P8133-22A/40KWFG4</b>	<b>P8133-28/40KWFG4</b>
Clear Alzak <sup>®</sup>	Gold Alzak <sup>®</sup>	White

## 8" RETROFIT HOUSING

Product No.	<b>P8215-EB120VG4</b>	
	<b>P8215-EB277VG4</b>	
Ceiling Opening	min. 8-1/8" max. 8-3/4"	
Product No.	<b>P8215-EBSD120VG4</b>	
<b>(Must use WF trims)</b>		
	<b>P8215-EBSD277VG4</b>	
Ceiling Opening	min. 7-15/16" max. 8-1/8"	
Ceiling Thickness	1-1/2"	
Plaster Frame	9" x 13-3/4" to 16"	
Pryouts	1/2" and 3/4"	

P8215-EB120VG4  
P8215-EB277VG4  
P8215-EBSD120VG4  
P8215-EBSD277VG4



## 3000 LUMEN OPEN MODULE TRIMS FOR P8215-EB

<b>P8120-21A/30KG4</b>	<b>P8120-22A/30KG4</b>	<b>P8120-28/30KG4</b>
<b>P8120-21A/35KG4</b>	<b>P8120-22A/35KG4</b>	<b>P8120-28/35KG4</b>
<b>P8120-21A/40KG4</b>	<b>P8120-22A/40KG4</b>	<b>P8120-28/40KG4</b>
Clear Alzak <sup>®</sup>	Gold Alzak <sup>®</sup>	White

## 3000 LUMEN OPEN MODULE TRIMS FOR P8215-EBSD

<b>P8120-21A/30KWFG4</b>	<b>P8120-22A/30KWFG4</b>	<b>P8120-28/30KWFG4</b>
<b>P8120-21A/35KWFG4</b>	<b>P8120-22A/35KWFG4</b>	<b>P8120-28/35KWFG4</b>
<b>P8120-21A/40KWFG4</b>	<b>P8120-22A/40KWFG4</b>	<b>P8120-28/40KWFG4</b>
Clear Alzak <sup>®</sup>	Gold Alzak <sup>®</sup>	White

- ### FEATURES
- Universal 120-277V high efficiency driver
  - Remote phosphor technology for controlled color consistency
  - 3000K, 3500K and 4000K options
  - 80+ CRI
  - 50 lumens per watt fixture efficacy
  - TM-21 50,000 hour life
  - J-box rated for (8) #12 90° conductors (4 in/4 out)
  - Suitable for wet locations, non-IC rated
  - 5 year warranty

- ### FEATURES
- 120V or 277V high efficiency driver
  - Remote phosphor technology for controlled color consistency
  - 3000K, 3500K and 4000K options
  - 80+ CRI
  - 50 lumens per watt fixture efficacy
  - TM-21 50,000 hour life
  - J-box rated for (8) #12 90° conductors (4 in/4 out)
  - Suitable for wet locations, non-IC rated
  - 5 year warranty



# 6" Pro-Optic<sup>®</sup> Firebox<sup>®</sup>

## 6" LED FIRE RATED HOUSING

Product No.	<b>P821-FBLED</b>
Ceiling Opening	6-7/8"
Recessed Depth	8-9/16"
Plaster Frame	12-3/8"- 9-9/16"
Pryouts	1/2" and 3/4"

P821-FBLED



## P8071 LED TRIMS (see page 58 for details)

**P8071-28/30K9-AC1-L07**  
**P8071-20/30K9-AC1-L07**  
**P8071-31/30K9-AC1-L07**  
**P8071-82/30K9-AC1-L07**  
 700 lumen



**P8071-28/30K9-L10-STR2**  
**P8071-28/35K9-L10-STR2**  
 1000 lumen



### FEATURES

- IC rated
- Fits into 2" x 10" construction
- CUL and UL listed for wet location when used w/P8071 (sold separately)
- UL classified to maintain fire ratings of 2 hour or less (see spec sheet for ceiling/floor designs)



## Recessed Accessories

### BAR HANGARS

Product No.	<b>P8716-01</b>
Description	Two 26" adjustable hangers for step lights, complete rounds and squares.

P8716-01



Product No.	<b>P8725-01</b>
Description	Bar Hangar for T-Bar. For use with P8200/8201/P82002/P8203

Product No.	<b>P8739-01</b>
Description	Bar Hangar for joist. For use with P8200/8201/P82002/P8203





## Outdoor

Landscape fixtures – including decorative lanterns, wall packs, cylinders and step lights – will enhance the exterior atmosphere and curb appeal, while adding safety and security to your property





## Outdoor Commercial LED Floodlights



PCOFL-30LED-20



PCOFL-50LED-20



PCOFL-100LED-20



PCOFL-200LED-20

Product No.	Finish	Lamp	Lumens	Size
<b>PCOFL-100LED-20</b>	Bronze	100w	8054	15" w., 7" ht., 6" d.
<b>PCOFL-200LED-20</b>		200w	16358	15" w., 14" ht., 6" d.
<b>PCOFL-30LED-20</b>		27w	2040	7.5" w., 5.125" ht., 4" d.
<b>PCOFL-50LED-20</b>		53w	4825	9.6" w., 6.7" ht., 4.5" d.



PCOGS-50LED-82



PCOGS-75LED-MS-82

## Commercial Garage / Surface LED

Product No.	Finish	Lamp	Size
<b>PCOGS-50LED-82</b>	Metallic Grey	15 LEDs, 53w, 4383 lumens	12.5" w., 5.21" ht., 12.01" d.
<b>PCOGS-75LED-82</b>		21 LEDs, 73w, 6040 lumens	
<b>PCOGS-50LED-MS-82</b>		15 LEDs, 53w, 4383 lumens	
<b>PCOGS-75LED-MS-82</b> Motion Sensor		21 LEDs, 73w, 6040 lumens	



PCVTS-LED



PCVTW-LED



PCVTS



PCVTW

## Vaportites

Product No.	Mount	Lamp	Size
<b>PCVTS</b>	Ceiling	150w inc.	4" w., 9" ht.
<b>PCVTS-LED</b>		LED, 11w, 757 lumens	5.2" w., 10.37" ht.
<b>PCVTW</b>	Wall	150w inc.	4" w., 9-3/4" ht., 7-1/4" d.
<b>PCVTW-LED</b>		LED, 11w, 757 lumens	5.2" w., 11" ht., 7.34" d.



PCOSL-30LED-82

## LED Dusk to Dawn

Product No.	Finish	Lamp	Size
<b>PCOSL-30LED-82</b>	Metallic Grey	LED, 30w, 2906 lumens	4" w., 16" ht., 9-1/2" d.

## LED Over Door Wall Pack

Product No.	Finish	Lamp	Size
<b>PCOMP-20LED-20</b>	Bronze	LED, 20w, 1513 lumens	5.39" w., 11.02" ht., 5.39" d.



PCOMP-20LED-20

## PCOWC SERIES LED Wall Pack

Product No.	Finish	Description	Lamp	Size
<b>PCOWC-20LED-20</b>	Bronze	Die-cast aluminum housing and door.	LED, 18w, 1421 lumens	8.22" w., 5.25" ht., 4.81" d.
<b>PCOWC-30LED-20</b>			LED, 29w, 2246 lumens	10.25" w., 14" ht., 6.25" d.
<b>PCOWC-45LED-20</b>			LED, 45w, 3096 lumens	
<b>PCOWC-20LED-28</b>	White		LED, 18w, 1421 lumens	8.22" w., 5.25" ht., 4.81" d.
<b>PCOWC-30LED-28</b>			LED, 29w, 2246 lumens	10.25" w., 14" ht., 6.25" d.
<b>PCOWC-45LED-28</b>			LED, 45w, 3096 lumens	
<b>PCOWC-20LED-82</b>	Metallic Gray		LED, 18w, 1421 lumens	8.22" w., 5.25" ht., 4.81" d.
<b>PCOWC-30LED-82</b>			LED, 29w, 2246 lumens	10.25" w., 14" ht., 6.25" d.
<b>PCOWC-45LED-82</b>			LED, 45w, 3096 lumens	



PCOWC-20LED-20



PCOWC-30LED-20



PCOWC-45LED-20

## PCOWF SERIES LED Wall Pack

Product No.	Finish	Description	Lens	Lamp	Size
<b>PCOWF-70LED-20LP</b>	Bronze	Die-cast aluminum housing	Glass	LED, 68w, 4505 lumens	14-7/8" w., 15" ht., 8" d.
<b>PCOWF-70LED-20LG</b>			Polycarbonate	LED, 68w, 5157 lumens	



PCOWF-70LED-20LG




PCOWF-70LED-20LP

## PCOWP SERIES LED Wall Pack

Product No.	Finish	Description	Lamp	Size
<b>PCOWP-50LED-20</b>	Bronze	Borosilicate glass refractor softens lamp image	LED, 53w, 4888 lumens	13" w., 9" ht., 7-1/4" d.
<b>PCOWP-100LED-20</b>			LED, 97w, 10151 lumens	13" w., 17" ht., 13" d.



PCOWP-50LED-20



PCOWP-100LED-20

## Quarter Sphere Wall Pack

Product No.	Finish	Description	Size	Lamps *included
<b>PHSL-13-23-B</b>	Antique Bronze	Die-cast aluminum housing with tempered, impact resistant clear glass lens. 23.3w input power. 1184 lumens. 120V/277V driver. 5000K color temperature.	12-3/4" w., 6-3/4" ht. Extends 7-3/4"	*One 23w LED module



PHSL-13-23-B

# LED Aluminum Cylinders

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing, Fade and chip-resistant. UL listed for wet locations when used with lens cover.

## FEATURES

- 120v AC
- 1000 source lumens (17w)  
2000 source lumens (29w)
- 3000K color temperature
- 90+ CRI
- Dimmable with many ELV type dimmers

## 6" ALUMINUM CYLINDERS

Product No. **P5641-20/30K** Bronze  
**P5641-30/30K** White  
**P5641-31/30K** Black  
**P5641-82/30K** Metallic Gray

Description One-light down (dark sky).

Size 6" W., 12" ht. Extends 8-7/8"  
H/CTR 4-1/2".

Lamp(s) One 29w LED module included.

Lumens 1560 delivered

P5641-30/30K



P5641-31/30K



P5641-82/30K



Product No. **P5642-20/30K** Bronze  
**P5642-30/30K** White  
**P5642-31/30K** Black  
**P5642-82/30K** Metallic Gray

Description Two-light up/down. For wet location specify P8798 top cover lens.

Size 6" W., 18" ht. Extends 8-7/8"  
H/CTR 8".

Lamp(s) Two 29w LED modules included.

Lumens 1560 delivered (up)  
1560 delivered (down)

P5642-20/30K



P5642-30/30K



P5642-82/30K



Product No. **P5741-20/30K** Bronze  
**P5741-30/30K** White  
**P5741-31/30K** Black

Description One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit (pg. 48).

Size 6" dia., 12" ht.

Lamp(s) One 29w LED module included.

Lumens 1560 delivered

P5741-20/30K



P5741-30/30K



P5741-31/30K



5" ALUMINUM CYLINDERS

Product No.	<b>P5674-20/30K</b> Bronze <b>P5674-30/30K</b> White <b>P5674-31/30K</b> Black <b>P5674-82/30K</b> Metallic Gray
Description	One-light down (dark sky).
Size	5" W., 7-1/4" ht. Extends 8". H/CTR 2-1/2".
Lamp	One 17w LED module included.
Lumens	820 delivered

P5674-82/30K



P5674-20/30K



P5674-30/30K



Product No.	<b>P5675-20/30K</b> Bronze <b>P5675-30/30K</b> White <b>P5675-31/30K</b> Black <b>P5675-82/30K</b> Metallic Gray
Description	Two-light up/down. For wet locations specify P8799 top cover lens.
Size	5" W., 14" ht. Extends 8". H/CTR 7".
Lamps	Two 17w LED modules included.
Lumens	820 delivered (up) 820 delivered (down)

P5675-82/30K



P5675-20/30K



P5675-31/30K



Product No.	<b>P5774-20/30K</b> Bronze <b>P5774-30/30K</b> White <b>P5774-31/30K</b> Black
Description	One-light. Mounts flush to ceiling (dark sky).
Size	5" dia., 6-1/2" ht.
Lamp	One 17w LED module included.
Lumens	820 delivered

P5774-20/30K



P5774-30/30K



P5774-31/30K





Westport LED offers traditional styling to complement a variety of home décor options. A durable, die-cast aluminum frame cradles a softly diffused, seeded glass shade

**FEATURES**

- 120v AC Replaceable LED module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)

Westport



P5864-3130K9

Product No.	Finish	Description	Size	Lamp *included
<b>P5862-2030K9</b> <b>P5862-3030K9</b> <b>P5862-3130K9</b>	Antique Bronze White Black	Small Wall Lantern	6-7/8" W., 10-1/4" ht. Extends 8-3/8". H/CTR 3-1/8".	*1 9w LED module
<b>P5863-2030K9</b> <b>P5863-3030K9</b> <b>P5863-3130K9</b>	Antique Bronze White Black	Medium Wall Lantern	9" W., 12-7/8" ht. Extends 10-3/8". H/CTR 3-3/4"	
<b>P5864-2030K9</b> <b>P5864-3030K9</b> <b>P5864-3130K9</b>	Antique Bronze White Black	Large Wall Lantern	11" W., 15-3/8" ht. Extends 12-7/8". H/CTR 4".	*1 17w LED module



P5862-2030K9



P5862-3030K9



P5863-2030K9



P5863-3130K9



P5864-2030K9



P3883-2030K9



P3883-3130K9

Product No.	Finish	Description	Size	Lamp *included
<b>P3883-2030K9</b> <b>P3883-3030K9</b> <b>P3883-3130K9</b>	Antique Bronze White Black	Flush Mount	9" dia., 7-1/4" ht.	*1 17w LED module





P5622-2030K9



P5622-8230K9



P5623-2030K9

## District



Product No.	Finish	Description	Size	Lamp *included
<b>P5622-2030K9</b>	Antique Bronze	Medium Wall Lantern	8" W., 8-1/4" ht.	*1 9w LED module
<b>P5622-8230K9</b>	Metallic Gray		Extends 10-1/4". H/CTR 4-1/8".	
<b>P5623-2030K9</b>	Antique Bronze	Large Wall Lantern	12" W., 10-1/2" ht.	
<b>P5623-8230K9</b>	Metallic Gray		Extends 13-1/4". H/CTR 5".	



P5623-8230K9



P6536-13630K9  
Ceiling



P6536-2030K9  
Ceiling



P6536-13630K9  
Pendant



P6536-2030K9  
Pendant

## Bell



Product No.	Finish	Description	Size	Lamp *included
<b>P6536-2030K9</b>	Antique Bronze	Ceiling / Pendant	6-5/8" dia., 11-3/8" ht.	*1 integral 9w LED module
<b>P6536-13630K9</b>	Textured Graphite		Overall ht. w/chain 77". wire 12".	
<b>P5676-2030K9</b>	Antique Bronze	Small Wall Lantern	5-1/2" W., 10-5/8" ht.	
<b>P5676-13630K9</b>	Textured Graphite		Extends 7-3/8". H/CTR 3".	



P5676-2030K9

P5676-13630K9

FEATURES

- 120v AC Replaceable LED module
- 17w: 1211 source lumens, 71.2 lumens/watt
- 9w: 623 source lumens, 69.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)

East Haven LED lanterns feature a die-cast aluminum powder coated frame with clear seeded glass.



# East Haven

Product No.	Finish	Description	Size	Lamp *included
<b>P6077-2030K9</b> <b>P6077-3130K9</b>	Antique Bronze Black	Small Wall Lantern	5-3/4" W., 7-7/8" ht. Extends 7-1/2". H/CTR 4-3/4"	*1 9w LED module
<b>P6078-2030K9</b> <b>P6078-3130K9</b>	Antique Bronze Black	Medium Wall Lantern	7-1/2" W., 9-1/2" ht. Extends 9-1/8". H/CTR 4-3/4"	
<b>P6079-2030K9</b> <b>P6079-3130K9</b>	Antique Bronze Black	Large Wall Lantern	9-1/2" W., 12" ht. Extends 11-1/8". H/CTR 4-3/4"	*1 17w LED module

P6079-2030K9



P6079-3130K9



P6078-2030K9



P6077-3130K9



P6078-3130K9



Product No.	Finish	Description	Size	Lamp *included
<b>P6430-2030K9</b> <b>P6430-3130K9</b>	Antique Bronze Black	Post Lantern	7-1/2" W., 15" ht. Extends 11-1/8". H/CTR 4-3/4"	*1 9w LED module

P6077-2030K9



Product No.	Finish	Description	Size	Lamp *included
<b>P6530-2030K9</b> <b>P6530-3130K9</b>	Antique Bronze Black	Hangin Lantern	7-1/2" W., 10-3/8" ht. Overall ht. w/chain 87"	*1 9w LED module



P6530-2030K9



P6530-3130K9



P6430-2030K9



P6430-3130K9



Wish LED lanterns feature a die-cast aluminum powder coated frame. Antique Bronze features etched amber linen glass. Black features etched white linen glass. Inner directional cylinder for **Dark Sky** compliance (cylinder is removable for traditional lighting).

**FEATURES**

- 120v AC Replaceable LED module
- 17w: source 1211 lumens, 71.2 lumens/watt
- 9w: 623 source lumens, 69.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)

Wish

Product No.	Finish	Description	Size	Lamp *included
<b>P6084-2030K9</b>	Antique Bronze	Medium Wall Lantern	7" W., 8-3/4" ht. Extends 8-5/8". H/CTR 3-1/8"	*1 9w LED module
<b>P6084-3130K9</b>	Black	Medium Wall Lantern	7" W., 8-3/4" ht. Extends 8-5/8". H/CTR 3-1/8"	*1 9w LED module
<b>P6085-2030K9</b>	Antique Bronze	Large Wall Lantern	9" W., 12-1/2" ht. Extends 10-1/2". H/CTR 3-1/8"	*1 17w LED module
<b>P6085-3130K9</b>	Black	Large Wall Lantern	9" W., 12-1/2" ht. Extends 10-1/2". H/CTR 3-1/8"	*1 17w LED module



P6085-3130K9



Dark Sky cylinder included



P6084-2030K9



P6084-3130K9

P6085-2030K9



Product No.	Finish	Description	Size	Lamp *included
<b>P6424-2030K9</b>	Antique Bronze	Post Lantern	9" W., 15-1/4" ht. Fits 3" post (order separately)	*1 9w LED module
<b>P6424-3130K9</b>	Black	Post Lantern	9" W., 15-1/4" ht. Fits 3" post (order separately)	*1 9w LED module

Product No.	Finish	Description	Size	Lamp *included
<b>P6524-2030K9</b>	Antique Bronze	Hanging Lantern	9" W., 12-1/2" ht.	*1 17w LED module
<b>P6524-3130K9</b>	Black	Hanging Lantern	Overall ht. w/chain 88"	*1 17w LED module



Dark Sky cylinder included

P6524-2030K9



P6524-3130K9



P6424-2030K9



P6424-3130K9



Arrive LED lanterns feature a die-cast aluminum powder coated frame and heavily textured glass.

**FEATURES**

- 120v AC Replaceable LED module
- 17w: 1211 source lumens, 71.2 lumens/watt
- 9w: 623 source lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- Dimmable with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)

Arrive



Product No.	Finish	Description	Size	Lamp *included
<b>P6067-3130K9</b>	Black	Small Wall Lantern	6" W., 8-3/4" ht. Extends 7-3/8". H/CTR 4"	*1 9w LED module
<b>P6068-3130K9</b>		Medium Wall Lantern	7-1/2" W., 11-1/8" ht. Extends 8-3/4". H/CTR 5-1/4"	
<b>P6069-3130K9</b>		Large Wall Lantern	9" W., 13" ht. Extends 10-1/4". H/CTR 5-3/4"	*1 17w LED module
<b>P6076-3130K9</b>		Extra Large Wall Lantern	11" W., 16" ht. Extends 12-1/4". H/CTR 8-5/8"	



P6067-3130K9



P6068-3130K9



P6427-3130K9



P6527-3130K9



P6069-3130K9

Product No.	Finish	Description	Size	Lamp *included
<b>P6427-3130K9</b>	Black	Post Lantern	9" sq., 15-7/8" ht. Fits 3" post (order separately)	*1 17w LED module



Product No.	Finish	Description	Size	Lamp *included
<b>P6527-3130K9</b>	Black	Hanging Lantern	9" sq., 15-1/8" ht. Overall ht. w/ chain 88-1/4"; wire 180"	*1 17w LED module



P6076-3130K9

**FEATURES**

- 120v AC Replaceable LED module
- 623 source lumens, 69.2 lumens/watt
- 3000K color temperature
- 90+ CRI
- Dimmable to 10% with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant

Endorse



Product No.	Finish	Description	Size	Lamp *included
<b>P6056-3130K9</b>	Black	Small Wall Lantern	6-3/4" W., 12" ht. Extends 7-5/8". H/CTR 3-1/4"	*1 9w LED module
<b>P6057-3130K9</b>		Medium Wall Lantern	8-3/4" W., 14-3/4" ht. Extends 9-3/4". H/CTR 4"	
<b>P6058-3130K9</b>		Large Wall Lantern	10-3/4" W., 17-3/4" ht. Extends 11-3/4". H/CTR 4"	



P6058-3130K9



P6056-3130K9  
Shown with P8774-31  
accessory column



P6057-3130K9



P6526-3130K9  
Shown with P8775-31  
accessory column



Product No.	Finish	Description	Size	Lamp *included
<b>P6526-3130K9</b>	Black	Large Wall Lantern	8-3/4" sq., 14-1/2" ht. Overall ht. w/chain 101"; wire 180"	*1 9w LED module

ACCESSORY COLUMNS

Product No.	<b>P8774-31</b> Black
Description	For use with P6056
Size	2-3/4" sq., 9-5/8" ht.

P8774-31



Product No.	<b>P8775-31</b> Black
Description	For use with P6057, P6526
Size	2-3/4" sq., 12-3/8" ht.

P8775-31



Product No.	<b>P8779-31</b> Black
Description	For use with P6058
Size	2-3/4" sq., 15-1/4" ht.

P8779-31





Get inspired from vintage undertones and train station styling with this energy efficient outdoor lantern collection. Available in aluminum with Gilded Iron finish, solid brass with Antique Nickel finish or Solid Copper that ages to a patina finish. Dark Sky compliant.

**FEATURES**

- 120v AC Replaceable LED module
- 1211 source lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant

Brookside



Product No.	Finish	Description	Size	Lamp *included
P5723-1430K9	Copper	Large Wall Lantern	12" W., 12-1/4" ht. Extends 13-1/4". H/CTR 6-7/8"	*1 17w LED module
P5723-7130K9	Gilded Iron			
P5723-8130K9	Antique Nickel			



P5723-1430K9



P5723-7130K9



P5723-8130K9



Craftsman styling marries traditional and rustic details. Derby boasts an artistic pattern glass diffuser with a die-cast aluminum, powder coated Antique Bronze frame.

**FEATURES**

- 120v AC Replaceable LED module
- 9w: 623 source lumens, 69.2 lumens/watt
- 17w: 1211 source lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant

Derby



Product No.	Finish	Description	Size	Lamp *included
<b>P5749-2030K9</b>		Small Wall Lantern	6-1/2" W., 8-3/8" ht. Extends 7-3/8". H/CTR 3"	
<b>P5750-2030K9</b>	Antique Bronze	Medium Wall Lantern	8-1/2" W., 11-1/4" ht. Extends 9-3/8". H/CTR 4-1/4"	*1 9w LED module
<b>P5751-2030K9</b>		Large Wall Lantern	10-5/8" W., 15-1/2" ht. Extends 11-5/8". H/CTR 3-3/8"	



P5749-2030K9



P5750-2030K9



P5751-2030K9



P6017-2030K9




Product No.	Finish	Description	Size	Lamp *included
<b>P6017-2030K9</b>	Antique Bronze	Flush Mount	10 sq." W., 5-1/2" ht.	*1 17w LED module

# Bulkheads

Die-cast aluminum frame with polycarbonate diffuser. Safety listed for wet locations. Wall or ceiling mount.

## FEATURES

- 120v AC Replaceable LED module
- 9w: 623 source lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable with many ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)

Product No.	<b>P3647-3030K9</b> White <b>P3647-3130K9</b> Black	
Description	One-light wall or close-to-ceiling	
Size	6-1/2" W., 10-1/2" ht. Extends 4-3/8". H/CTR 5-14".	
Lamp	One 9w LED module included.	

P3647-3030K9




*Shown as wall mount*



P3647-3130K9



Product No.	<b>P3648-3030K9</b> White <b>P3648-3130K9</b> Black	
Description	One-light round wall or close-to-ceiling	
Size	9-1/2" W., 4-3/8" ht. Extends 4-3/8". H/CTR 4-3/4".	
Lamp	One 17w LED module included.	

P3648-3030K9




P3648-3130K9



*Shown as wall mount*



Product No.	<b>P3649-3030K9</b> White <b>P3649-3130K9</b> Black	
Description	One-light wall or close-to-ceiling	
Size	6-1/2" W., 10-1/2" ht. Extends 4-1/2". H/CTR 5-14".	
Lamp	One 9w LED module included.	

P3649-3030K9




P3649-3130K9



*Shown as wall mount*



Product No.	<b>P3650-3030K9</b> White <b>P3650-3130K9</b> Black	
Description	One-light round wall or close-to-ceiling	
Size	9-1/2" W., 4-3/8" ht. Extends 4-1/2". H/CTR 4-3/4".	
Lamp	One 17w LED module included.	

P3650-3030K9



*Shown as wall mount*



P3650-3130K9



## Security Lighting

THESE LED SWIVEL FLOOD LIGHTS HAVE TEMPERED GLASS AND RUGGED DIE CAST CONSTRUCTION. CAN BE USED AS SINGLE OR MULTIPLE HEADS. ORDER BACKPLATE AND FLOODLIGHT SEPARATELY.



P6342-20/30K9



P6342-20/30K9



P6342-82/30K9



P6343-20  
shown with (2) P6342-20/30K heads



P6343-20

Product No.	Finish	Size	Lamp
<b>P6342-20/30K</b>	Antique Bronze	3-3/4" W. , 5" ht. Extends 3-1/4"	13w LED module
<b>P6342-28/30K</b>	White		
<b>P6342-82/30K</b>	Metallic Gray		

Product No.	Finish	Size
<b>P6343-20</b>	Antique Bronze	4-1/2" dia.
<b>P6343-28</b>	White	
<b>P6343-82</b>	Metallic Gray	

Five KO gaskets included. Die cast aluminum construction.



PEOEU-EM-20

## Decorative LED AC/Emergency Light

Series	Description	Finish	Size	Lumens
<b>PEOEU-EM-09</b>	Emergency Battery	Brushed Nickel	6.54" w., 10.47" ht., 3.78" d.	AC Mode - 223
<b>PEOEU-EM-20</b>		Bronze		
<b>PEOEU-EM-30</b>		White		
<b>PEOEU-EM-09-HTR</b>	Emergency Battery w/ heater option	Brushed Nickel		DC Mode - 261 (Running on Emergency Battery)
<b>PEOEU-EM-20-HTR</b>		Bronze		
<b>PEOEU-EM-30-HTR</b>		White		



P3715-31

## Non-Metallic

Series	Finish	Description	Size	Lamp
<b>P3715-31</b>	Black	120V/277V input voltage. Durable non-corrosive UV resistant housing. 4000K, 912 lumens. 74+ CRI. Wet location listed.	6" W., 9" ht. H/CTR 4-1/4"	LED array 10w.

## Step Lights



P6827-0930K

Product No.	Finish	Description	Size	Lamp *included
<b>P6827-0930K</b>	Brushed Nickel	Louvered horizontal step/wall light. Wet location listed.	5-1/4" W. , 3-1/2" ht.	4w LED module, 100 lumens, 25 lumens/watt
<b>P6827-3030K</b>	Antique Bronze			
<b>P6827-2030K</b>	White			
<b>P6827-3130K</b>	Black			

P6827-3030K



P6827-2030K



P6827-3130K



P6828-0930K

Product No.	Finish	Description	Size	Lamp *included
<b>P6828-0930K</b>	Brushed Nickel	Louvered vertical step/wall light. Wet location listed.	3-1/2" W. , 5-1/4" ht.	4w LED module, 100 lumens, 25 lumens/watt
<b>P6828-3030K</b>	Antique Bronze			
<b>P6828-2030K</b>	White			
<b>P6828-3130K</b>	Black			

P6828-2030K



P6828-3030K



P6828-3130K



P6829-0930K

Product No.	Finish	Description	Size	Lamp *included
<b>P6829-0930K</b>	Brushed Nickel	Horizontal step/wall light. Wet location listed.	2-7/8" W. , 4-1/2" ht.	4w LED module, 84 lumens, 21 lumens/watt
<b>P6829-3030K</b>	Antique Bronze			
<b>P6829-2030K</b>	White			
<b>P6829-3130K</b>	Black			

P6829-3030K



P6829-2030K



P6829-3130K



P6832-0930K

Product No.	Finish	Description	Size	Lamp *included
<b>P6832-0930K</b>	Brushed Nickel	Vertical step/wall light. Wet location listed.	2-7/8" W. , 4-1/2" ht.	4w LED module 65 lumens, 16 lumens/watt
<b>P6832-3030K</b>	Antique Bronze			
<b>P6832-2030K</b>	White			
<b>P6832-3130K</b>	Black			

P6832-3030K



P6832-2030K



P6832-3130K







## Area / Site

From parking lots to pools, Progress Lighting's energy efficient outdoor products create a well-lit environment with low maintenance benefits.






## PCPAE Series

### ECONOMY SERIES PARKING/SITE LUMINAIRE


The PCPAE Series is designed for parking and area lighting applications utilizing high power LEDs, capable of replacing up to 400W traditional HID luminaires. The PCPAE is offered in 11,000 lumen and 16,000 lumen versions, available with Type 3 and Type 5 optics.


Series	Wattage	Lumens	Distribution	Finish
PCPAE	125 - 16 LEDs, 123w	11150 - 11260	3 - Type 3	BZ - Bronze
	180 - 24 LEDs, 181w	16360 - 16510	5 - Type 5	

**TYPE 3** (PCPAE-125-3)



**TYPE 5** (PCPAE-125-5)





MTO


## PCPA Series

PERFORMANCE SERIES  
PARKING/SITE LUMINAIRE


The PCPAS and PCPAL Series is designed for parking and area lighting applications utilizing high power LEDs, capable of replacing up to 400W traditional HID luminaires. The PSPAS is offered in 8,000 lumen versions. The PSPAL is offered in 14,000 lumen and 18,000 lumen versions. All models available with Type 3 and Type 5 optics.

Series	Wattage	Lumens	Distribution	Finish	Options
<b>PCPAS</b> - Parking Area Small	<b>90</b> - 30 LEDs, 90w	7900 - 8100	<b>3</b> - Type 3	<b>BZ</b> - Bronze	Blank
<b>PCPAL</b> - Parking Area Large	<b>135</b> - 64 LEDs, 135w	13740 - 14950	<b>5</b> - Type 5	<b>BL</b> - Black	<b>P</b> - Photocell
	<b>180</b> - 80 LEDs, 180w	17150 - 18670	Square	<b>GN</b> - Green	

**TYPE 3** (PCPAS-90-3)



**TYPE 5** (PCPAS-90-5)






## PCADS/PCADL Series

### DESIGNER SERIES PARKING/SITE LUMINAIRE


The PCADS and PCADL series is designed for parking and area lighting applications utilizing high power LEDs while providing contemporary aesthetics. The PSADS/PCADL is offered in 4,800 lumen, 6,800 lumen and 9,800 lumen versions. All models available with Type 3 and Type 5 optics.

Series	Size	Wattage	Distribution	Finish	Options
<b>PCAD</b>	<b>S</b> - Small	<b>55</b> - Small or Large	<b>3</b> - Type 3	<b>BZ</b> - Bronze	Blank
	<b>L</b> - Large	<b>80</b> - Small or Large	<b>5</b> - Type 5	<b>BL</b> - Bronze	<b>P</b> - Photocell
		<b>80</b> - Large		<b>GN</b> - Green	<b>CR</b> - Cast Rings

**TYPE 3 (PCADS-80-3)**







## Poles

Constructed with exacting standards both our aluminum and steel products meet strict guidelines for quality, strength and finish durability. Protecting your investment for years is our Lektrocote® powder paint finish, available in bronze, black and textured green. From shaft cutting through finishing, quality control inspections are conducted throughout a highly automated process.

### Steel Products

Series	Construction	Shaft Sizes	Wall Thickness	Lengths
<b>SSS-P</b>	Square Straight Steel	4", 5", 6"	11 GA, 7 GA, 3 GA	10 – 40 ft
<b>RSS-P</b>	Round Straight Steel	3", 4", 4.5", 5", 6"	11 GA, 7 GA, 3 GA	8 – 30 ft
<b>STS-P</b>	Square Tapered Steel	5" – 9"	11 GA, 7 GA	20 – 50 ft
<b>RTS-P</b>	Round Tapered Steel	5" – 12"	11 GA, 7 GA	10 – 60 ft

### Aluminum Products

Series	Construction	Shaft Sizes	Wall Thickness	Lengths
<b>SSS-P</b>	Square Straight Steel	4", 5", 6"	.125", .188", .250"	10 – 40 ft
<b>RSS-P</b>	Round Straight Steel	3", 4", 4.5", 5", 6"	.125", .188", .250"	8 – 30 ft
<b>RTS-P</b>	Round Tapered Steel	4" – 8"	.125", .188", .220", .250"	8 – 40 ft

RSS-P

SSS-P



PCOGS-50LED-82



PCOGS-75LED-MS-82

## Commercial Garage / Surface LED

Product No.	Finish	Lamp	Size
<b>PCOGS-50LED-82</b>	Metallic Grey	15 LEDs, 53w, 4383 lumens	12.5" w., 5.21" ht., 12.01" d.
<b>PCOGS-75LED-82</b>		21 LEDs, 73w, 6040 lumens	
<b>PCOGS-50LED-MS-82</b>		15 LEDs, 53w, 4383 lumens	
<b>PCOGS-75LED-MS-82</b> Motion Sensor		21 LEDs, 73w, 6040 lumens	





PCPTD

## LED Post Top Designer

MTO

Series	Wattage	Distribution	Finish	Options	Lumens
<b>PCPTD</b>	<b>80</b> - 36 LEDs, 80w	<b>3</b> - Type 3 <b>5</b> - Type 5 Round Wide	<b>BZ</b> - Bronze <b>BL</b> - Black <b>GN</b> - Green	Blank <b>P</b> - Photocell <b>FG</b> - Frosted Acrylic Globe	6440 - 6950

Size: 18-7/16" w., 36" h.

## LED Post Top Shade

MTO

Series	Wattage	Distribution	Finish	Options
<b>PCPTS</b>	<b>80</b> - 36 LEDs, 80w	<b>3</b> - Type 3 <b>5</b> - Type 5 Round Wide	<b>BZ</b> - Bronze <b>BL</b> - Black <b>GN</b> - Green	Blank <b>P</b> - Photocell

Size: 25-1/2" w., 24-1/4" h.



PCPTS

## LED Post Top Globe

MTO

Series	Wattage	Distribution	Finish	Options	Lumens
<b>PCPTG</b>	<b>55</b> - 24 LEDs, 55w	<b>3</b> - Type 3 <b>5</b> - Type 5 Round Wide	<b>BZ</b> - Bronze <b>BL</b> - Black <b>GN</b> - Green	Blank <b>P</b> - Photocell <b>MB</b> - Metal band	3600 - 4000

Size: 16-3/5" w., 25" h.



PCPTG



PCPTT

## LED Post Top Traditional

MTO

Series	Wattage	Distribution	Finish	Options
<b>PCPTT</b>	<b>27</b> - 24 LEDs, 27w <b>80</b> - 36 LEDs, 80w	<b>3</b> - Type 3 <b>5</b> - Type 5 Round Wide	<b>BZ</b> - Bronze <b>BL</b> - Black <b>GN</b> - Green	Blank <b>P</b> - Photocell

Size: 10-3/4" w., 21-3/4" h.



PCBOR

PCBOS

## Walkway Lighting

MTO

Series	Wattage	Finish
<b>PCBOR</b> - Bollard Round	<b>ASY</b> - 12 LEDs, 31w	<b>BZ</b> - Bronze
<b>PCBOS</b> - Bollard Square	<b>SYM</b> - 24 LEDs, 46w	<b>BL</b> - Black

Size: Round - 6.75" sq., 42" h. Square - 7" diam., 42" h.



## HID Area Shoe Box



MTO

Series	Wattage	Distribution	Finish	Options
<b>PCPMH</b>	<b>100</b> - 100w Metal Halide	<b>3</b> - Type 3	<b>BZ</b> - Bronze	Blank
	<b>150</b> - 100w Metal Halide	<b>5</b> - Type 5	<b>BL</b> - Black	<b>L</b> - Lamp Included
	<b>250</b> - 250w Metal Halide			
	<b>420</b> - 400w Metal Halide			



PCPMH

# ASCE7-05 WIND MAP



Note:  
Florida Building Code may  
supercede national map.



## Wind Map Notes

- Values are based on 50 year mean recurrence interval 30' above grade.
- Hawaii has an **105** mph wind velocity.
- Puerto Rico has a **125** mph wind velocity.
- Caution must be exercised in determining wind velocities in special wind areas such as:
  - Mountainous Regions
  - Areas surrounding the Great Lakes or other large bodies of water or open land.
  - Areas subject to extreme wind conditions, such as hurricanes, typhoons, cyclones, and tornadoes.
  - Areas adjacent to airports.
  - Any specific area with a known or suspected abnormally high intermittent wind condition caused by geography, adjacent structures, or other specific local conditions that may not be recorded in National Weather Service records.
- Allowable pole EPA for jobsite wind conditions must be equal to or greater than fixture EPA. Responsibility lies with the specifier for correct pole selection based on ASCE7-05 wind map and job location.
- The Wind Map is intended only as a general guide. Always consult local authorities to determine maximum wind velocities, gusting and unique wind conditions for each specific application.

## Caution

- Wind speeds and listed EPAs are for ground mounted installations. Poles mounted on structures (such as bridges and buildings) must consider vibration and coefficient of height factors beyond this general guide. Consult AASHTO standards.
- Extreme Wind Events: Hurricanes, Typhoons, Cyclones, or Tornadoes expose poles to flying debris, wind shear, and other unpredictable aerodynamic forces not indicated by the wind velocity ratings.
- Pole Strength Limited Warranty: Standard, unmodified Progress Commercial Lighting Poles installed as recommended, undamaged by corrosion, or lack of maintenance, shall withstand steady wind conditions on each pole's Allowable Pole EPA chart. Installation of poles without luminaires, or attachment of any unauthorized accessories to poles shall void this warranty.

## EPA Information

All allowable pole and fixture EPAs (Fixture Area x Drag Factor) are derived from the AASHTO standard (American Association of State Highway and Transportation Officials). Responsibility lies with the specifier for correct pole selection based on local codes and standards for the job location.

To obtain more information on AASHTO Standards for Lighting Equipment contact:

American Association of State Highway  
and Transportation Officials  
444 N. Capitol Street, NW, Suite 249  
Washington, DC 20001  
202 624-5800  
[www.aashto.org](http://www.aashto.org)

AASHTO standards used are found in the following publications: I-LTS-4 "Standard Specification for Structural Support for Highway Signs, Luminaires and Traffic Signals," (2001).

## Important

Do not erect poles without luminaires in place. Any accessories attached to pole, or other modifications will compromise pole strength and may result in pole failure.

## Maintenance

A regularly scheduled maintenance program must be established to insure the protective paint coating is intact, corrosion or structural damage has not occurred, and anchor bolt nuts are tight. Failure to do so could lead to pole collapse and personal injury.

Lamps not included with fixtures unless specified. Specifications subject to change without notice.

©Progress Lighting 2016

All rights reserved.  
International copyright secured.

## LINEAR /TROFFER

PCICT	4
PCILS	6
PCILT	4
PCILW	5
PCIPG	6
PCIRK	6
PCIST	4
PCISW	6
PCIVT	6
PCIWB	5
P7137	6
P7154	6
P7183	5
P7186	5
P7189	6
P7196	5
P7206	8
P7218	8
P7221	8
P7249	7
P7250	7
P7251	7
P7252	7
P7258	7
P7265	5
P7266	5
P7267	5
P7268	5
P7278	8
P7279	8
P7280	8
P7285	8

## EMERGENCY / EXIT

PE2EU	10
PE2WL	13
PEALE	12
PECLB	14
PECUE	10
PEEMB	13
PEERE	11
PEESE	11
PEHWU	12
PEOEU	13
PERHC	11
PETPE	10
PEWLE	12
PEWLH	13

## CLOSE-TO-CEILING

P2300	25
P2301	25
P2302	24
P2303	24
P2304	25
P2305	25
P2306	22
P2307	22
P2308	22
P2309	22
P2310	22
P2311	22

P7329	27
P7379	31
P7381	31
P7382	31
P7383	30
P7384	30
P7385	22,30
P8022	16
P8027	16
P8222	17
P8107	17
P8240	18
P8241	18
P8247	18
P8147	19

## CEILING FANS

P2514	35
P2530	34
P2531	34
P2602	36
P2620	36
P2621	36
P2658	36

## SCONCES

P5790	40
P5800	42
P5801	42
P5806	42
P5914	42
P5915	42
P7044	40
P7045	40
P7052	39
P7068	39
P7081	39
P7082	39
P7083	38
P7085	38
P7092	38
P7093	38,40
P7163	40
P7249	38

## BATH AND VANITY

P2004	48
P2005	48
P2006	48
P2061	44
P2062	44
P2063	44
P2064	44
P2091	45
P2092	45
P2093	45
P2094	45
P2142	45
P2143	45
P2144	45
P2145	45
P2706	48
P2707	48

P2708	48
P2709	48
P7025	46
P7114	47
P7115	47
P7116	47
P7211	46
P7212	46
P7218	46
P7221	46
P7227	46
P7228	46
P7229	46
P7230	47
P7231	47
P7232	47
P7236	47
P7237	47

## HANGING

P3468	57
P3474	58
P3912	59
P4275	57
P4276	57
P4324	58
P4328	58
P4329	58
P4365	58
P4440	60
P4441	60
P4621	59
P4623	59
P4627	60
P4715	50
P5023	51
P5024	51
P5053	50
P5075	50
P5087	53
P5094	53
P5096	58
P5113	60
P5143	50
P5145	57
P5175	51
P5176	51
P5187	51
P5197	52
P5300	59
P5551	52
P5535	52
P5623	52
P7322	57
P7323	57
P8768	54
P8769	54
P8825	54
P8830	54
P8820	54
P8821	54
P8828	54
P8928	54

## UNDERCABINET

P7002	62
P7005	62
P7012	62
P7013	62
P7510	63
P8733	63
P8735	63
P8737	63
P8738	63
P8740	63
P8743	63

## RECESSED

P87	66
P821	72
P830	67
P831	67
P832	67
P8061	67
P8064	68
P8067	68
P8071	66,72
P8080	67
P8102	71
P8103	70
P8104	69
P8105	69
P8106	69
P8120	70,71
P8121	70,71
P8133	70,71
P8152	68
P8153	68
P8206	68
P8215	71
P8216	69
P8220	70
P8556	68
P8716	72
P8725	72

## OUTDOOR

PCOFL	74
PCOGS	74
PCOMP	75
PCOSL	74
PCOWC	75
PCOWF	75
PCOWP	75
PCVTS	74
PCVTW	74
PEOEU	88
PHSL	75
P3647	86
P3648	86
P3649	86
P3650	86
P3715	88
P3883	78
P5622	79
P5623	79
P5641	76

P5642	76
P5674	77
P5675	77
P5676	79
P5723	84
P5741	76
P5749	85
P5750	85
P5751	85
P5774	77
P5862	78
P5863	78
P5864	78
P6017	85
P6056	83
P6057	83
P6058	83
P6067	82
P6068	82
P6069	82
P6076	82
P6077	80
P6078	80
P6079	80
P6084	81
P6085	81
P6342	87
P6343	87
P6424	81
P6427	82
P6430	80
P6524	81
P6526	83
P6527	82
P6530	80
P6536	79
P6827	88
P6828	88
P6829	88
P6832	88
P8774	83
P8775	83
P8779	83

## AREA / SITE

PCBOR	96
PCBOS	96
PCPMH	97
PCAD	92
PCOG	93
PCPA	91
PCPAE	90
PCPTD	94
PCPTG	95
PCPTS	95
PCPTT	96
RSS	93
RTS	9
SSS	9
STS	9





# PROGRESS

COMMERCIAL LIGHTING

Progress Commercial Lighting

701 Millennium Boulevard  
Greenville, South Carolina  
29607

[progresscommercial.com](http://progresscommercial.com)

