

INVITE



P4696-20

Here is your invitation to understated elegance. Iconic scroll arms and dual-layer etched glass and translucent mylar drum shades. Optional clear cylindrical acrylic finials offer high style.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO AVAILABLE IN

Bath & Vanity
Close-to-Ceiling

PAIR WITH

Baycourt



WALL BRACKET

P2041-20 Antique Bronze
6-1/2" W., 11-1/2" ht.
Extends 8-1/4". H/CTR 3-3/4".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3694-20 Antique Bronze
Hanging and ceiling mount
hardware included.
15" dia., 5-1/4" ht.
Overall ht. w/stem 71"; wire 12'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4695-20 Antique Bronze
22" dia., 19-3/4" ht.
Overall ht. w/stem 86"; wire 12'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4696-20 Antique Bronze
25-1/4" dia., 20-3/4" ht.
Overall ht. w/stem 87"; wire 12'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4697-20 Antique Bronze
Two-tier.
35-5/8" dia., 26-1/2" ht. Overall ht.
w/stem 92"; wire 15'.
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER

P4725-20 Antique Bronze
Three-tier.
49" dia., 38" ht.
Overall ht. w/chain 161"; wire 12'.
Twelve medium base lamps,
each 75w max.

TWO-LIGHT FOYER PENDANT

P5046-20 Antique Bronze
14" dia., 30-1/4" ht.
Overall ht. w/stem 96"; wire 15'.
Two medium base T10 lamps,
each 60w max.

FOUR-LIGHT PENDANT

P5047-20 Antique Bronze
20" dia., 27-3/8" ht.
Overall ht. w/stem 93"; wire 12'.
Four medium base lamps,
each 100w max.

MINI-PENDANT

P5110-20 Antique Bronze
6-1/2" dia., 7-3/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.



P5047-20



P4695-20



P3694-20



P4697-20



P5046-20



P5110-20



P4725-20



P2041-20



Shown: P4697-20 chandelier
(image: Kolter Homes)



P4695-09
shown without
optional finial



P4696-09



P5047-09




P3694-09



P5046-09



P4697-09



P5110-09



P4725-20



P5046-09



P5047-09

INVITE

WALL BRACKET

P2041-09 Brushed Nickel
6-1/2" W., 11-1/2" ht.
Extends 8-1/4". H/CTR 3-3/4".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3694-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
15" dia., 5-1/4" ht.
Overall ht. w/stem 71"; wire 12".
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4695-09 Brushed Nickel
22" dia., 19-3/4" ht.
Overall ht. w/stem 86"; wire 12".
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4696-09 Brushed Nickel
25-1/4" dia., 20-3/4" ht.
Overall ht. w/stem 87"; wire 12".
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4697-09 Brushed Nickel
Two-tier.
35-5/8" dia., 26-1/2" ht.
Overall ht. w/stem 92"; wire 12".
Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER

P4725-09 Brushed Nickel
Three-tier.
49" dia., 38" ht.
Overall ht. w/chain 161"; wire 15".
Twelve medium base lamps,
each 75w max.

TWO-LIGHT FOYER PENDANT

P5046-09 Brushed Nickel
14" dia., 30-1/4" ht.
Overall ht. w/stem 96"; wire 15".
Two medium base T10 lamps,
each 60w max.

FOUR-LIGHT PENDANT

P5047-09 Brushed Nickel
20" dia., 27-3/8" ht.
Overall ht. w/stem 93"; wire 12".
Four medium base lamps,
each 100w max.

MINI-PENDANT

P5110-09 Brushed Nickel
6-1/2" dia., 7-3/8" ht.
Overall ht. w/stem 74"; wire 10".
One medium base lamp,
100w max.

INVITE



Dual-layer etched glass and mylar drum shades on a Brushed Nickel or Antique Bronze frame.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ALSO AVAILABLE IN

Fixture Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2041-20 Antique Bronze
6-1/2" W., 11-1/2" ht.
Extends 8-1/4". H/CTR 3-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P2078-20 Antique Bronze
14-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2079-20 Antique Bronze
23-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2080-20 Antique Bronze
32-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH

P2081-20 Antique Bronze
41-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Five medium base lamps,
each 100w max.



P2041-20



P2078-20



P2079-20



P2080-20



P2081-20



P2041-09



P2078-09



P2079-09



P2080-09



P2081-09

ONE-LIGHT BATH

P2041-09 Brushed Nickel
6-1/2" W., 11-1/2" ht.
Extends 8-1/4". H/CTR 3-3/4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P2078-09 Brushed Nickel
14-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2079-09 Brushed Nickel
23-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2080-09 Brushed Nickel
32-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Four medium base lamps,
each 100w max.

FIVE-LIGHT BATH

P2081-09 Brushed Nickel
41-1/2" W., 7-3/8" ht.
Extends 7-1/2". H/CTR 4-7/8".
Five medium base lamps,
each 100w max.

INVITE

Etched glass with translucent mylar drum shade.

TWO-LIGHT FLUSH MOUNT

P3693-09 Brushed Nickel

P3693-20 Antique Bronze
12" dia., 5-3/8" ht.

Two medium base lamps,
each 60w max.



P3693-20



P3693-09

SEMI-FLUSH CONVERTIBLE

P3694-09 Brushed Nickel

P3694-20 Antique Bronze
Hanging and ceiling mount
hardware included.

15" dia., 5-1/4" ht.

Overall ht. w/stem 71"; wire 12'

Three medium base lamps,
each 100w max.



P3694-20



P3694-09