

THE
BASICS
BOOK



BASICS



NUVO[®]

Nuvo has the essentials.

And the designs. And the efficiency. And the choices.

From charming and versatile indoor home packages to the simple yet beautiful variations on the standards, the Nuvo name has become synonymous with the well-crafted products that deliver quality, value and style. Any venue, large or small, indoors or out, would benefit from these timeless designs. Simply put, Nuvo Lighting offers the most well thought-out fixture collections on the market today.

We launched Nuvo Lighting in 2005 with more than 1,500 new lighting fixtures, and a belief that good value should also be beautiful, manufactured to the highest standards of quality and suitable for projects large or small. It's the reason our product line and business has grown every year since. With Satco's more than 45 years of industry experience behind us, we've been able to introduce one of the industry's broadest ranges of innovative lighting fixtures available today.

Nuvo. There's so much to design.

Contents

Dupont	6	Wall and Flush	172
Interior Home Packages.	14	Industrial Style	
Chandeliers	70	Surface Mount.	174
Pendants	71	Carport Flushmounts	176
Close to Ceiling.	73	Utility Fixtures	177
Vanity and Wall	87	Porch Wall Fixtures.	178
Ceiling / Wall	90	Poly Lanterns.	180
Track Lighting	92	Halogen Exterior	
Dupont ES.	110	Floodlights	181
Interior Home ES Packages.	118	Exterior Floodlights	182
ES Wall Fixtures	150	Landscape Floodlights	186
ES Ceiling Fixtures	152	Pathway Lighting	188
OUTDOOR.	160	Twistlock Globes.	190
Central Park	162	Twistlock Holders /	
Cornerstone.	164	Pier Mount Bases	191
Briton	166	Cornerstone ES	192
Small Wall Lanterns	168	Small Wall Lanterns ES	194
Die Cast Bulkheads	170	INDEX	196



On the cover: Nuvo Lighting's Interior Home Collection's 15" Pendant in Brushed Nickel with Alabaster Glass, page 40

On the opposite page: Nuvo Lighting's ENERGY STAR® certified Dupont five light 'convertible' chandelier (shown arms down) in Brushed Nickel with Satin White glass, page 110

contents

Refining the classics.



Nuvo Incandescent

As Nuvo works to make advanced lighting more mainstream, we're also working to make mainstream lighting beautiful and impactful. Our incandescent collections bring clean, unadorned lines and fresh new looks and finishes to the most popular fixture types.

Lighting fixtures are one very visible part of any home or building project -- and with lighting fixtures, style is (almost) everything.

Nuvo incandescent fixtures are constructed of the finest materials and manufactured to the highest standards of quality. And rest assured: Nuvo delivers the style today's buyers are looking for.



impactful

Dupont is an affordable collection which offers quality and style. Fine details such as rich finishes, finely crafted Satin White glassware and great attention to construction are evident throughout.

DUPONT



Two Tier – Nine Light Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 27 1/2", Height 23 1/2", Chain 72", Wire 12'

60-1823 Brushed Nickel / Satin White Glass

Accessories:

25-1069 3' Section of matching chain



Three Light Chandelier

(3) 60W A19 max. / Medium Base
Dimensions: Width 17", Height 13½", Chain 48", Wire 12'
60-1821 Brushed Nickel / Satin White Glass
Convertible – Arms up or Down
Accessories:
25-1069 3' Section of matching chain



Small Flush Dome

(1) 100W A19 max. / Medium Base
Dimensions: Width 11", Height 7"
60-1824 Brushed Nickel / Satin White Glass
CUL damp location



Mini Pendant

(1) 60W A19 max. / Medium Base
Dimensions: Width 6", Height 42" Adjustable, Wire 12'
60-1831 Brushed Nickel / Satin White Glass
Accessories:
Additional Stem Lengths
25-2047 (6"), **25-2021** (12")



Medium Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13", Height 7"
60-1825 Brushed Nickel / Satin White Glass
CUL damp location



Semi-Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 16", Height 15½", Wire 12'
60-1827 Brushed Nickel / Satin White Glass
Convertible to pendant
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



Large Flush Dome

(2) 75W A19 max. / Medium Base
Dimensions: Width 15", Height 7¾"
60-1826 Brushed Nickel / Satin White Glass
CUL damp location



DUPONT



Five Light Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 22", Height 15³/₄", Chain 48", Wire 12'

60-1822 Brushed Nickel / Satin White Glass

Convertible – Arms up or Down

Accessories:

25-1069 3' Section of matching chain



Three Light Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 16", Height 20", Chain 48", Wire 12"
60-1828 Brushed Nickel / Satin White Glass
Accessories:
25-1069 3' Section of matching chain



Two Light Vanity

(2) 100W A19 max. / Medium Base
Dimensions: Width 13", Height 8", Extension 7³/₄"
60-1833 Brushed Nickel / Satin White Glass



Hanging Dome

(1) 100W A19 max. / Medium Base
Dimensions: Width 16", Height 10¹/₂", Chain 48", Wire 12"
60-1829 Brushed Nickel / Satin White Glass
Accessories:
25-1069 3' Section of matching chain



Three Light Vanity

(3) 100W A19 max. / Medium Base
Dimensions: Width 24", Height 8", Extension 7³/₄"
60-1834 Brushed Nickel / Satin White Glass



One Light Vanity

(1) 100W A19 max. / Medium Base
Dimensions: Width 6", Height 8", Extension 8¹/₂"
60-1832 Brushed Nickel / Satin White Glass



Four Light Vanity

(4) 100W A19 max. / Medium Base
Dimensions: Width 30", Height 8", Extension 7³/₄"
60-1835 Brushed Nickel / Satin White Glass



DUPONT



Two Tier – Nine Light Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 27 1/2", Height 23 1/2", Chain 72", Wire 12'

60-1843 Dark Chocolate Bronze / Satin White Glass

Accessories:

25-3024 3' Section of matching chain



Three Light Chandelier

(3) 60W A19 max. / Medium Base
Dimensions: Width 17", Height 13½", Chain 48", Wire 12'
60-1841 Dark Chocolate Bronze / Satin White Glass
Convertible – Arms up or Down
Accessories:
25-3024 3' Section of matching chain



Small Flush Dome

(1) 100W A19 max. / Medium Base
Dimensions: Width 11", Height 7"
60-1844 Dark Chocolate Bronze / Satin White Glass
CUL damp location



Mini Pendant

(1) 60W A19 max. / Medium Base
Dimensions: Width 6", Height 42" Adjustable, Wire 12'
60-1851 Dark Chocolate Bronze / Satin White Glass
Accessories:
Additional Stem Lengths
25-4007 (6"), **25-4008** (12")



Medium Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13", Height 7"
60-1845 Dark Chocolate Bronze / Satin White Glass
CUL damp location



Semi-Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 16", Height 15½", Wire 12'
60-1847 Dark Chocolate Bronze / Satin White Glass
Convertible to pendant
Accessories:
25-3073 Pendant conversion kit
25-3024 3' Section of matching chain



Large Flush Dome

(2) 75W A19 max. / Medium Base
Dimensions: Width 15", Height 7¾"
60-1846 Dark Chocolate Bronze / Satin White Glass
CUL damp location



DUPONT



Five Light Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 22", Height 15³/₄", Chain 48", Wire 12'

60-1842 Dark Chocolate Bronze / Satin White Glass

Convertible – Arms up or Down

Accessories:

25-3024 3' Section of matching chain



Three Light Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 16", Height 20", Chain 48", Wire 12'
60-1848 Dark Chocolate Bronze / Satin White Glass
Accessories:
25-3024 3' Section of matching chain



Two Light Vanity

(2) 100W A19 max. / Medium Base
Dimensions: Width 13", Height 8", Extension 7³/₄"
60-1853 Dark Chocolate Bronze / Satin White Glass



Hanging Dome

(1) 100W A19 max. / Medium Base
Dimensions: Width 16", Height 10¹/₂", Chain 48", Wire 12'
60-1849 Dark Chocolate Bronze / Satin White Glass
Accessories:
25-3024 3' Section of matching chain



Three Light Vanity

(3) 100W A19 max. / Medium Base
Dimensions: Width 24", Height 8", Extension 7³/₄"
60-1854 Dark Chocolate Bronze / Satin White Glass



One Light Vanity

(1) 100W A19 max. / Medium Base
Dimensions: Width 6", Height 8", Extension 8¹/₂"
60-1852 Dark Chocolate Bronze / Satin White Glass



Four Light Vanity

(4) 100W A19 max. / Medium Base
Dimensions: Width 30", Height 8", Extension 7³/₄"
60-1855 Dark Chocolate Bronze / Satin White Glass



Old Bronze with Alabaster Glass

This traditional Old Bronze finish is complemented by Alabaster glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME PACKAGE



Two Tier - Nine Light Empire Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-362 Old Bronze / Alabaster Glass

Accessories:

25-1067 3' Section of matching chain



Five Light Ballerina Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 18", Chain 48", Wire 12'

60-183 Old Bronze / Alabaster Glass

Accessories:

25-1067 3' Section of matching chain



Five Light Gotham Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'

60-191 Old Bronze / Alabaster Glass

Accessories:

25-1067 3' Section of matching chain



Three Light Ballerina Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 17", Chain 48", Wire 12'

60-184 Old Bronze / Alabaster Glass

Accessories:

25-1067 3' Section of matching chain



Three Light Gotham Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'

60-192 Old Bronze / Alabaster Glass

Accessories:

25-1067 3' Section of matching chain



Six Light Empire Chandelier

(6) 60W A19 max. / Medium Base

Dimensions: Width 26", Height 14", Chain 48", Wire 12'

60-358 Old Bronze / Alabaster Glass

Accessories:

25-1067 3' Section of matching chain

Old Bronze with
Alabaster Glass

INTERIOR HOME PACKAGE



20" Pendant

(5) 60W A19 max. / Medium Base
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-212 Old Bronze / Alabaster Glass
Accessories:
25-1067 3' Section of matching chain



15" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-211 Old Bronze / Alabaster Glass
Accessories:
25-1067 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-210 Old Bronze / Alabaster Glass
Accessories:
25-1402 Pendant conversion kit
25-1067 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-209 Old Bronze / Alabaster Glass
Accessories:
25-1402 Pendant conversion kit
25-1067 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-208 Old Bronze / Alabaster Glass
Accessories:
25-1402 Pendant conversion kit
25-1067 3' Section of matching chain



11" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 4⁷/₈"
60-205 Old Bronze / Alabaster Glass
CUL damp location



12" Twist and Lock

(1) 60W A19 max. / Medium Base
Dimensions: Width 11¹/₂", Height 4¹/₂"
60-280 Old Bronze / Alabaster Glass
CUL damp location



13" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 5³/₈"
60-206 Old Bronze / Alabaster Glass
CUL damp location



14" Twist and Lock

(2) 60W A19 max. / Medium Base
Dimensions: Width 14", Height 5¹/₂"
60-281 Old Bronze / Alabaster Glass
CUL damp location



15" Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 6"
60-207 Old Bronze / Alabaster Glass
CUL damp location



17" Twist and Lock

(3) 60W A19 max. / Medium Base
Dimensions: Width 17", Height 6"
60-282 Old Bronze / Alabaster Glass
CUL damp location

interior home package

Old Bronze with
Alabaster Glass

INTERIOR HOME PACKAGE



6" Flush Ball

(1) 60W A19 max. / Medium Base
Dimensions: Width 6", Height 7 1/4"
60-259 Old Bronze / Alabaster Glass
CUL damp location



12" Tri-Clip Flush Dome

(1) 60W A19 max. / Medium Base
Dimensions: Width 12 1/2", Height 4"
60-272 Old Bronze / Alabaster Glass

16" Tri-Clip Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 16 1/8", Height 5"
60-273 Old Bronze / Alabaster Glass



Pendant Bell

(1) 100W A19 max. / Medium Base
Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'
60-395 Old Bronze / Alabaster Glass
Accessories:
25-1067 3' Section of matching chain



Hanging Dome

(1) 100W A19 max. / Medium Base
Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'
60-391 Old Bronze / Alabaster Glass
Accessories:
25-1067 3' Section of matching chain



Empire Mini Pendant

with hang-straight canopy
(1) 100W A19 max. / Medium Base
Dimensions: Width 7", Height 51" Adjustable, Wire 12'
60-366 Old Bronze / Alabaster Glass
Accessories:
Additional Stem Lengths
25-2028 (6"), **25-2002** (12")



Ballerina Three Light 24" Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"

60-325 Old Bronze / Alabaster Glass



Ballerina Four Light 30" Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"

60-326 Old Bronze / Alabaster Glass



Ballerina Two Light 18" Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"

60-324 Old Bronze / Alabaster Glass



Ballerina Five Light 36" Vanity

(5) 100W A19 max. / Medium Base

Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"

60-327 Old Bronze / Alabaster Glass



Ballerina One Light Sconce

(1) 60W A19 max. / Medium Base

Dimensions: Width 15⁷/₈", Height 7", Extension 7⁷/₈"

60-5378 Old Bronze / Alabaster Glass

(glass up installation only)



Ballerina Seven Light 48" Vanity

(7) 100W A19 max. / Medium Base

Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"

60-292 Old Bronze / Alabaster Glass

interior home package

Old Bronze with
Alabaster Glass

INTERIOR HOME PACKAGE



Empire One Light Sconce

(1) 60W A19 max. / Medium Base
Dimensions: Width 10", Height 9⁵/₈", Extension 5"
60-5374 Old Bronze / Alabaster Glass
(glass up installation only)



Empire Two Light Vanity

(2) 100W A19 max. / Medium Base
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-345 Old Bronze / Alabaster Glass



Empire Three Light Vanity

(3) 100W A19 max. / Medium Base
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-346 Old Bronze / Alabaster Glass



Empire One Light Vanity

(1) 100W A19 max. / Medium Base
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-344 Old Bronze / Alabaster Glass



Empire Four Light Vanity

(4) 100W A19 max. / Medium Base
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-347 Old Bronze / Alabaster Glass



24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base
 Dimensions: Width 24", Height 4¾",
 Extension 2" (less lamp)

60-305 Old Bronze



36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base
 Dimensions: Width 36", Height 4¾",
 Extension 2" (less lamp)

60-306 Old Bronze



18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base
 Dimensions: Width 18", Height 4¾",
 Extension 2" (less lamp)

60-304 Old Bronze



48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base
 Dimensions: Width 48", Height 4¾",
 Extension 2" (less lamp)

60-307 Old Bronze

interior home package

Mahogany Bronze
with Champagne Linen
Washed Glass Shades

Deep rich Mahogany Bronze is accented
by Champagne Linen glass in this
complete product grouping which
offers a fixture for every application.

INTERIOR HOME PACKAGE



Two Tier - Nine Light Empire Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-1275 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain





Five Light Ballerina Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 18", Chain 48", Wire 12'

60-1251 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain



Five Light Gotham Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'

60-1253 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain



Three Light Ballerina Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 17", Chain 48", Wire 12'

60-1252 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain



Three Light Gotham Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'

60-1254 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain



Six Light Empire Chandelier

(6) 60W A19 max. / Medium Base

Dimensions: Width 26", Height 14", Chain 48", Wire 12'

60-1274 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain

Mahogany Bronze
with Champagne Linen
Washed Glass Shades

INTERIOR HOME PACKAGE



20" Pendant

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'

60-1263 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain



15" Pendant

(3) 60W A19 max. / Medium Base

Dimensions: Width 15", Height 23", Chain 48", Wire 12'

60-1262 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base

Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'

60-1261 Mahogany Bronze / Champagne Glass

Accessories:

25-2082 Pendant conversion kit

25-2081 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base

Dimensions: Width 13¹/₄", Height 14", Wire 12'

60-1259 Mahogany Bronze / Champagne Glass

Accessories:

25-2082 Pendant conversion kit

25-2081 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base

Dimensions: Width 11³/₈", Height 12", Wire 12'

60-1258 Mahogany Bronze / Champagne Glass

Accessories:

25-2082 Pendant conversion kit

25-2081 3' Section of matching chain



11" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/8", Height 4 7/8"
60-1255 Mahogany Bronze / Champagne Glass
CUL damp location



12" Twist and Lock

(1) 60W A19 max. / Medium Base
Dimensions: Width 11 1/2", Height 4 1/2"
60-1281 Mahogany Bronze / Champagne Glass
CUL damp location



13" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13 1/4", Height 5 3/8"
60-1256 Mahogany Bronze / Champagne Glass
CUL damp location



14" Twist and Lock

(2) 60W A19 max. / Medium Base
Dimensions: Width 14", Height 5 1/2"
60-1282 Mahogany Bronze / Champagne Glass
CUL damp location



15" Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 15 1/4", Height 6"
60-1257 Mahogany Bronze / Champagne Glass
CUL damp location



17" Twist and Lock

(3) 60W A19 max. / Medium Base
Dimensions: Width 17", Height 6"
60-1283 Mahogany Bronze / Champagne Glass
CUL damp location

Mahogany Bronze
with Champagne Linen
Washed Glass Shades

INTERIOR HOME PACKAGE



Hanging Dome

(1) 100W A19 max. / Medium Base

Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'

60-1276 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain



Pendant Bell

(1) 100W A19 max. / Medium Base

Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'

60-1278 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain



6" Flush Ball

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 7 1/4"

60-1279 Mahogany Bronze / Champagne Glass

CUL damp location



Empire Mini Pendant

with hang-straight canopy

(1) 100W A19 max. / Medium Base

Dimensions: Width 7", Height 51" Adjustable, Wire 12'

60-1277 Mahogany Bronze / Champagne Glass

Accessories:

Additional Stem Lengths

25-2078 (6"), **25-2079** (12")



Ballerina Three Light 24" Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"

60-1265 Mahogany Bronze / Champagne Glass



Ballerina Four Light 30" Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"

60-1266 Mahogany Bronze / Champagne Glass



Ballerina Two Light 18" Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"

60-1264 Mahogany Bronze / Champagne Glass



Ballerina Five Light 36" Vanity

(5) 100W A19 max. / Medium Base

Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"

60-1267 Mahogany Bronze / Champagne Glass



Ballerina One Light Sconce

(1) 60W A19 max. / Medium Base

Dimensions: Width 15⁷/₈", Height 7", Extension 7⁷/₈"

60-5384 Mahogany Bronze / Champagne Glass

(glass up installation only)



Ballerina Seven Light 48" Vanity

(7) 100W A19 max. / Medium Base

Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"

60-1268 Mahogany Bronze / Champagne Glass

interior home package

Mahogany Bronze
with Champagne Linen
Washed Glass Shades

INTERIOR HOME PACKAGE



Empire One Light Sconce

(1) 60W A19 max. / Medium Base
Dimensions: Width 10", Height 9⁵/₈", Extension 5"
60-5383 Mahogany Bronze / Champagne Glass
(glass up installation only)



Empire Two Light Vanity

(2) 100W A19 max. / Medium Base
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-1271 Mahogany Bronze / Champagne Glass



Empire Three Light Vanity

(3) 100W A19 max. / Medium Base
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-1272 Mahogany Bronze / Champagne Glass



Empire One Light Vanity

(1) 100W A19 max. / Medium Base
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-1269 Mahogany Bronze / Champagne Glass



Empire Four Light Vanity

(4) 100W A19 max. / Medium Base
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-1273 Mahogany Bronze / Champagne Glass



24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base
 Dimensions: Width 24", Height 4¾",
 Extension 2" (less lamp)
60-1285 Mahogany Bronze



36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base
 Dimensions: Width 36", Height 4¾",
 Extension 2" (less lamp)
60-1286 Mahogany Bronze



18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base
 Dimensions: Width 18", Height 4¾",
 Extension 2" (less lamp)
60-1284 Mahogany Bronze



48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base
 Dimensions: Width 48", Height 4¾",
 Extension 2" (less lamp)
60-1287 Mahogany Bronze

interior home package

Mahogany Bronze with Frosted White Glass Shades

Deep rich Mahogany Bronze is accented by Frosted White glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME PACKAGE



Two Tier - Nine Light Empire Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-3171 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain





Five Light Ballerina Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 18", Chain 48", Wire 12'

60-3141 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain



Five Light Gotham Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'

60-3143 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain



Three Light Ballerina Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 17", Chain 48", Wire 12'

60-3142 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain



Three Light Gotham Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'

60-3144 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain



Six Light Empire Chandelier

(6) 60W A19 max. / Medium Base

Dimensions: Width 26", Height 14", Chain 48", Wire 12'

60-3169 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain

Mahogany Bronze with
Frosted White Glass Shades

INTERIOR HOME PACKAGE



20" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-3153 Mahogany Bronze / Frosted Glass
Accessories:
25-2081 3' Section of matching chain



15" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-3152 Mahogany Bronze / Frosted Glass
Accessories:
25-2081 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-3151 Mahogany Bronze / Frosted Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-3149 Mahogany Bronze / Frosted Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-3148 Mahogany Bronze / Frosted Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain



11" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 4⁷/₈"
60-3145 Mahogany Bronze / Frosted Glass
CUL damp location



12" Twist and Lock

(1) 60W A19 max. / Medium Base
Dimensions: Width 11¹/₂", Height 4¹/₂"
60-3175 Mahogany Bronze / Frosted Glass
CUL damp location



13" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 5³/₈"
60-3146 Mahogany Bronze / Frosted Glass
CUL damp location



14" Twist and Lock

(2) 60W A19 max. / Medium Base
Dimensions: Width 14", Height 5¹/₂"
60-3176 Mahogany Bronze / Frosted Glass
CUL damp location



15" Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 6"
60-3147 Mahogany Bronze / Frosted Glass
CUL damp location



17" Twist and Lock

(3) 60W A19 max. / Medium Base
Dimensions: Width 17", Height 6"
60-3177 Mahogany Bronze / Frosted Glass
CUL damp location

interior home package

Mahogany Bronze with
Frosted White Glass Shades



INTERIOR HOME PACKAGE



Hanging Dome

(1) 100W A19 max. / Medium Base

Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'

60-3173 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain



Pendant Bell

(1) 100W A19 max. / Medium Base

Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'

60-3174 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain



6" Flush Ball

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 7 1/4"

60-3154 Mahogany Bronze / Frosted Glass

CUL damp location



Empire Mini Pendant

with hang-straight canopy

(1) 100W A19 max. / Medium Base

Dimensions: Width 7", Height 51" Adjustable, Wire 12'

60-3172 Mahogany Bronze / Frosted Glass

Accessories:

Additional Stem Lengths

25-2078 (6"), **25-2079** (12")



Ballerina Three Light 24" Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"

60-3162 Mahogany Bronze / Frosted Glass



Ballerina Four Light 30" Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"

60-3163 Mahogany Bronze / Frosted Glass



Ballerina Two Light 18" Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"

60-3161 Mahogany Bronze / Frosted Glass



Ballerina Five Light 36" Vanity

(5) 100W A19 max. / Medium Base

Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"

60-3164 Mahogany Bronze / Frosted Glass



Ballerina One Light Sconce

(1) 60W A19 max. / Medium Base

Dimensions: Width 15⁷/₈", Height 7", Extension 7⁷/₈"

60-5379 Mahogany Bronze / Frosted Glass

(glass up installation only)



Ballerina Seven Light 48" Vanity

(7) 100W A19 max. / Medium Base

Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"

60-3155 Mahogany Bronze / Frosted Glass

interior home package

Mahogany Bronze with
Frosted White Glass Shades

INTERIOR HOME PACKAGE



Empire One Light Sconce

(1) 60W A19 max. / Medium Base
Dimensions: Width 10", Height 9⁵/₈", Extension 5"
60-5375 Mahogany Bronze / Frosted Glass
(glass up installation only)



Empire Two Light Vanity

(2) 100W A19 max. / Medium Base
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-3166 Mahogany Bronze / Frosted Glass



Empire Three Light Vanity

(3) 100W A19 max. / Medium Base
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-3167 Mahogany Bronze / Frosted Glass



Empire One Light Vanity

(1) 100W A19 max. / Medium Base
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-3165 Mahogany Bronze / Frosted Glass



Empire Four Light Vanity

(4) 100W A19 max. / Medium Base
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-3168 Mahogany Bronze / Frosted Glass



24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base
Dimensions: Width 24", Height 4³/₄",
Extension 2" (less lamp)
60-1285 Mahogany Bronze



36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base
Dimensions: Width 36", Height 4³/₄",
Extension 2" (less lamp)
60-1286 Mahogany Bronze



18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base
Dimensions: Width 18", Height 4³/₄",
Extension 2" (less lamp)
60-1284 Mahogany Bronze



48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base
Dimensions: Width 48", Height 4³/₄",
Extension 2" (less lamp)
60-1287 Mahogany Bronze

Brushed Nickel with Alabaster Glass Shades

Brushed Nickel is accented by Alabaster glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME PACKAGE



Two Tier - Nine Light Empire Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-360 Brushed Nickel / Alabaster Glass

Accessories:

25-1069 3' Section of matching chain





Five Light Ballerina Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 18", Chain 48", Wire 12'

60-181 Brushed Nickel / Alabaster Glass

Accessories:

25-1069 3' Section of matching chain



Five Light Gotham Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'

60-189 Brushed Nickel / Alabaster Glass

Accessories:

25-1069 3' Section of matching chain



Three Light Ballerina Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 17", Chain 48", Wire 12'

60-182 Brushed Nickel / Alabaster Glass

Accessories:

25-1069 3' Section of matching chain



Three Light Gotham Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'

60-190 Brushed Nickel / Alabaster Glass

Accessories:

25-1069 3' Section of matching chain



Six Light Empire Chandelier

(6) 60W A19 max. / Medium Base

Dimensions: Width 26", Height 14", Chain 48", Wire 12'

60-356 Brushed Nickel / Alabaster Glass

Accessories:

25-1069 3' Section of matching chain

interior home package

Brushed Nickel with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



20" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-204 Brushed Nickel / Alabaster Glass
Accessories:
25-1069 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-202 Brushed Nickel / Alabaster Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-201 Brushed Nickel / Alabaster Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-200 Brushed Nickel / Alabaster Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain

15" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-203 Brushed Nickel / Alabaster Glass
Accessories:
25-1069 3' Section of matching chain



11" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 4⁷/₈"
60-197 Brushed Nickel / Alabaster Glass
CUL damp location



12" Twist and Lock

(1) 60W A19 max. / Medium Base
Dimensions: Width 11¹/₂", Height 4¹/₂"
60-283 Brushed Nickel / Alabaster Glass
CUL damp location



13" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 5³/₈"
60-198 Brushed Nickel / Alabaster Glass
CUL damp location



14" Twist and Lock

(2) 60W A19 max. / Medium Base
Dimensions: Width 14", Height 5¹/₂"
60-284 Brushed Nickel / Alabaster Glass
CUL damp location



15" Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 6"
60-199 Brushed Nickel / Alabaster Glass
CUL damp location



17" Twist and Lock

(3) 60W A19 max. / Medium Base
Dimensions: Width 17", Height 6"
60-285 Brushed Nickel / Alabaster Glass
CUL damp location

Brushed Nickel with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



6" Flush Ball

(1) 60W A19 max. / Medium Base
Dimensions: Width 6", Height 7 1/4"
60-257 Brushed Nickel / Alabaster Glass
CUL damp location



12" Tri-Clip Flush Dome

(1) 60W A19 max. / Medium Base
Dimensions: Width 12 1/2", Height 4"
60-270 Brushed Nickel / Alabaster Glass

16" Tri-Clip Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 16 1/8", Height 5"
60-271 Brushed Nickel / Alabaster Glass



Pendant Bell

(1) 100W A19 max. / Medium Base
Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'
60-394 Brushed Nickel / Alabaster Glass
Accessories:
25-2081 3' Section of matching chain



Hanging Dome

(1) 100W A19 max. / Medium Base
Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'
60-390 Brushed Nickel / Alabaster Glass
Accessories:
25-1069 3' Section of matching chain



Empire Mini Pendant

with hang-straight canopy
(1) 100W A19 max. / Medium Base
Dimensions: Width 7", Height 5 1/2" Adjustable, Wire 12'
60-365 Brushed Nickel / Alabaster Glass
Accessories:
Additional Stem Lengths
25-2047 (6"), **25-2021** (12")



Ballerina Three Light 24" Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"

60-321 Brushed Nickel / Alabaster Glass



Ballerina Four Light 30" Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"

60-322 Brushed Nickel / Alabaster Glass



Ballerina Two Light 18" Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"

60-320 Brushed Nickel / Alabaster Glass



Ballerina Five Light 36" Vanity

(5) 100W A19 max. / Medium Base

Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"

60-323 Brushed Nickel / Alabaster Glass



Ballerina One Light Sconce

(1) 60W A19 max. / Medium Base

Dimensions: Width 15⁷/₈", Height 7", Extension 7⁷/₈"

60-5381 Brushed Nickel / Alabaster Glass

(glass up installation only)



Ballerina Seven Light 48" Vanity

(7) 100W A19 max. / Medium Base

Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"

60-291 Brushed Nickel / Alabaster Glass

interior home package

Brushed Nickel with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



Empire One Light Sconce

(1) 60W A19 max. / Medium Base
Dimensions: Width 10", Height 9⁵/₈", Extension 5"
60-5376 Brushed Nickel / Alabaster Glass
(glass up installation only)



Empire Two Light Vanity

(2) 100W A19 max. / Medium Base
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-341 Brushed Nickel / Alabaster Glass



Empire Three Light Vanity

(3) 100W A19 max. / Medium Base
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-342 Brushed Nickel / Alabaster Glass



Empire One Light Vanity

(1) 100W A19 max. / Medium Base
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-340 Brushed Nickel / Alabaster Glass



Empire Four Light Vanity

(4) 100W A19 max. / Medium Base
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-343 Brushed Nickel / Alabaster Glass



24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base
Dimensions: Width 24", Height 4¾",
Extension 2" (less lamp)

60-301 Brushed Nickel



36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base
Dimensions: Width 36", Height 4¾",
Extension 2" (less lamp)

60-302 Brushed Nickel



18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base
Dimensions: Width 18", Height 4¾",
Extension 2" (less lamp)

60-300 Brushed Nickel



48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base
Dimensions: Width 48", Height 4¾",
Extension 2" (less lamp)

60-303 Brushed Nickel

Brushed Nickel with Frosted White Glass Shades

Brushed Nickel is accented by Frosted White glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME PACKAGE



Two Tier - Nine Light Empire Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-3256 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain





Five Light Ballerina Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 18", Chain 48", Wire 12'

60-3240 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain



Five Light Gotham Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'

60-3242 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain



Three Light Ballerina Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 17", Chain 48", Wire 12'

60-3241 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain



Three Light Gotham Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'

60-3243 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain



Six Light Empire Chandelier

(6) 60W A19 max. / Medium Base

Dimensions: Width 26", Height 14", Chain 48", Wire 12'

60-3255 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain

Brushed Nickel with
Frosted White Glass Shades

INTERIOR HOME PACKAGE



20" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-3248 Brushed Nickel / Frosted Glass
Accessories:
25-1069 3' Section of matching chain



15" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-3247 Brushed Nickel / Frosted Glass
Accessories:
25-1069 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-3246 Brushed Nickel / Frosted Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-3245 Brushed Nickel / Frosted Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-3244 Brushed Nickel / Frosted Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11³/₈", Height 4⁷/₈"

60-3261 Brushed Nickel / Frosted Glass

CUL damp location



12" Twist and Lock

(1) 60W A19 max. / Medium Base

Dimensions: Width 11¹/₂", Height 4¹/₂"

60-3271 Brushed Nickel / Frosted Glass

CUL damp location



13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13¹/₄", Height 5³/₈"

60-3262 Brushed Nickel / Frosted Glass

CUL damp location



14" Twist and Lock

(2) 60W A19 max. / Medium Base

Dimensions: Width 14", Height 5¹/₂"

60-3272 Brushed Nickel / Frosted Glass

CUL damp location



15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15¹/₄", Height 6"

60-3263 Brushed Nickel / Frosted Glass

CUL damp location



17" Twist and Lock

(3) 60W A19 max. / Medium Base

Dimensions: Width 17", Height 6"

60-3273 Brushed Nickel / Frosted Glass

CUL damp location

Brushed Nickel with
Frosted White Glass Shades

INTERIOR HOME PACKAGE



Hanging Dome

(1) 100W A19 max. / Medium Base
Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'
60-3258 Brushed Nickel / Frosted Glass
Accessories:
25-1069 3' Section of matching chain



Pendant Bell

(1) 100W A19 max. / Medium Base
Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'
60-3259 Brushed Nickel / Frosted Glass
Accessories:
25-1069 3' Section of matching chain



6" Flush Ball

(1) 60W A19 max. / Medium Base
Dimensions: Width 6", Height 7 1/4"
60-3249 Brushed Nickel / Frosted Glass
CUL damp location



Empire Mini Pendant

with hang-straight canopy
(1) 100W A19 max. / Medium Base
Dimensions: Width 7", Height 51" Adjustable, Wire 12'
60-3257 Brushed Nickel / Frosted Glass
Accessories:
Additional Stem Lengths
25-2047 (6"), **25-2021** (12")



Ballerina Three Light 24" Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"

60-3279 Brushed Nickel / Frosted Glass



Ballerina Four Light 30" Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"

60-3281 Brushed Nickel / Frosted Glass



Ballerina Two Light 18" Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"

60-3278 Brushed Nickel / Frosted Glass



Ballerina Five Light 36" Vanity

(5) 100W A19 max. / Medium Base

Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"

60-3282 Brushed Nickel / Frosted Glass



Ballerina One Light Sconce

(1) 60W A19 max. / Medium Base

Dimensions: Width 15⁷/₈", Height 7", Extension 7⁷/₈"

60-5382 Brushed Nickel / Frosted Glass

(glass up installation only)



Ballerina Seven Light 48" Vanity

(7) 100W A19 max. / Medium Base

Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"

60-3283 Brushed Nickel / Frosted Glass

interior home package

Brushed Nickel with
Frosted White Glass Shades

INTERIOR HOME PACKAGE



Empire One Light Sconce

(1) 60W A19 max. / Medium Base
Dimensions: Width 10", Height 9⁵/₈", Extension 5"
60-5377 Brushed Nickel / Frosted Glass
(glass up installation only)



Empire Two Light Vanity

(2) 100W A19 max. / Medium Base
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-3265 Brushed Nickel / Frosted Glass



Empire Three Light Vanity

(3) 100W A19 max. / Medium Base
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-3266 Brushed Nickel / Frosted Glass



Empire One Light Vanity

(1) 100W A19 max. / Medium Base
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-3264 Brushed Nickel / Frosted Glass



Empire Four Light Vanity

(4) 100W A19 max. / Medium Base
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-3277 Brushed Nickel / Frosted Glass



24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base
Dimensions: Width 24", Height 4³/₄",
Extension 2" (less lamp)

60-301 Brushed Nickel



36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base
Dimensions: Width 36", Height 4³/₄",
Extension 2" (less lamp)

60-302 Brushed Nickel



18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base
Dimensions: Width 18", Height 4³/₄",
Extension 2" (less lamp)

60-300 Brushed Nickel



48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base
Dimensions: Width 48", Height 4³/₄",
Extension 2" (less lamp)

60-303 Brushed Nickel

Polished Brass with Alabaster Glass Shades

Polished Brass is accented by Alabaster glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME PACKAGE



Two Tier - Nine Light Empire Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-361 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



Five Light Ballerina Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 18", Chain 48", Wire 12'

60-185 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



Five Light Gotham Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'

60-193 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



Three Light Ballerina Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 17", Chain 48", Wire 12'

60-186 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



Three Light Gotham Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'

60-194 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



Six Light Empire Chandelier

(6) 60W A19 max. / Medium Base

Dimensions: Width 26", Height 14", Chain 48", Wire 12'

60-357 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain

interior home package

Polished Brass with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



20" Pendant

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'

60-220 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



15" Pendant

(3) 60W A19 max. / Medium Base

Dimensions: Width 15", Height 23", Chain 48", Wire 12'

60-219 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15 1/4", Height 15 1/2", Wire 12'

60-218 Polished Brass / Alabaster Glass

Accessories:

25-1401 Pendant conversion kit

25-1066 3' Section of matching chain



11" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/8", Height 4 7/8"

60-213 Polished Brass / Alabaster Glass

CUL damp location



13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 13 1/4", Height 14", Wire 12'

60-217 Polished Brass / Alabaster Glass

Accessories:

25-1401 Pendant conversion kit

25-1066 3' Section of matching chain



13" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13 1/4", Height 5 3/8"

60-214 Polished Brass / Alabaster Glass

CUL damp location



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/8", Height 12", Wire 12'

60-216 Polished Brass / Alabaster Glass

Accessories:

25-1401 Pendant conversion kit

25-1066 3' Section of matching chain



15" Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 15 1/4", Height 6"

60-215 Polished Brass / Alabaster Glass

CUL damp location

Polished Brass with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



6" Flush Ball

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 7 1/4"

60-255 Polished Brass / Alabaster Glass

CUL damp location



12" Tri-Clip Flush Dome

(1) 60W A19 max. / Medium Base

Dimensions: Width 12 1/2", Height 4"

60-274 Polished Brass / Alabaster Glass

16" Tri-Clip Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 16 1/8", Height 5"

60-275 Polished Brass / Alabaster Glass



Pendant Bell

(1) 100W A19 max. / Medium Base

Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'

60-396 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



Hanging Dome

(1) 100W A19 max. / Medium Base

Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'

60-392 Polished Brass / Alabaster Glass

Accessories:

25-1066 3' Section of matching chain



Empire Mini Pendant

with hang-straight canopy

(1) 100W A19 max. / Medium Base

Dimensions: Width 7", Height 5 1/2" Adjustable, Wire 12'

60-367 Polished Brass / Alabaster Glass

Accessories:

Additional Stem Lengths

25-2046 (6"), **25-2019** (12")



Ballerina Four Light 30" Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"

60-330 Polished Brass / Alabaster Glass



Ballerina Three Light 24" Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"

60-329 Polished Brass / Alabaster Glass



Ballerina Five Light 36" Vanity

(5) 100W A19 max. / Medium Base

Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"

60-331 Polished Brass / Alabaster Glass



Ballerina Two Light 18" Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"

60-328 Polished Brass / Alabaster Glass



Ballerina Seven Light 48" Vanity

(7) 100W A19 max. / Medium Base

Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"

60-293 Polished Brass / Alabaster Glass

Polished Brass with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



Empire Two Light Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"

60-349 Polished Brass / Alabaster Glass



Empire Three Light Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"

60-350 Polished Brass / Alabaster Glass



Empire One Light Vanity

(1) 100W A19 max. / Medium Base

Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"

60-348 Polished Brass / Alabaster Glass



Empire Four Light Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"

60-351 Polished Brass / Alabaster Glass



24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base
Dimensions: Width 24", Height 4³/₄",
Extension 2" (less lamp)
60-309 Polished Brass



36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base
Dimensions: Width 36", Height 4³/₄",
Extension 2" (less lamp)
60-310 Polished Brass



18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base
Dimensions: Width 18", Height 4³/₄",
Extension 2" (less lamp)
60-308 Polished Brass



48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base
Dimensions: Width 48", Height 4³/₄",
Extension 2" (less lamp)
60-311 Polished Brass

Textured White with Alabaster Glass Shades

Textured White is accented by Alabaster glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME PACKAGE



Two Tier - Nine Light Empire Chandelier

(9) 60W A19 max. / Medium Base

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-363 Textured White / Alabaster Glass

Accessories:

25-1072 3' Section of matching chain



Five Light Ballerina Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 18", Chain 48", Wire 12'

60-187 Textured White / Alabaster Glass

Accessories:

25-1072 3' Section of matching chain



Five Light Gotham Chandelier

(5) 60W A19 max. / Medium Base

Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'

60-195 Textured White / Alabaster Glass

Accessories:

25-1072 3' Section of matching chain



Three Light Ballerina Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 17", Chain 48", Wire 12'

60-188 Textured White / Alabaster Glass

Accessories:

25-1072 3' Section of matching chain



Three Light Gotham Chandelier

(3) 60W A19 max. / Medium Base

Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'

60-196 Textured White / Alabaster Glass

Accessories:

25-1072 3' Section of matching chain



Six Light Empire Chandelier

(6) 60W A19 max. / Medium Base

Dimensions: Width 26", Height 14", Chain 48", Wire 12'

60-359 Textured White / Alabaster Glass

Accessories:

25-1072 3' Section of matching chain

Textured White with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



20" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-228 Textured White / Alabaster Glass
Accessories:
25-1072 3' Section of matching chain



15" Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-227 Textured White / Alabaster Glass
Accessories:
25-1072 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-226 Textured White / Alabaster Glass
Accessories:
25-1404 Pendant conversion kit
25-1072 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-225 Textured White / Alabaster Glass
Accessories:
25-1404 Pendant conversion kit
25-1072 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-224 Textured White / Alabaster Glass
Accessories:
25-1404 Pendant conversion kit
25-1072 3' Section of matching chain



11" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 11³/₈", Height 4⁷/₈"
60-221 Textured White / Alabaster Glass
CUL damp location



12" Twist and Lock

(1) 60W A19 max. / Medium Base
Dimensions: Width 11¹/₂", Height 4¹/₂"
60-286 Textured White / Alabaster Glass
CUL damp location



13" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13¹/₄", Height 5³/₈"
60-222 Textured White / Alabaster Glass
CUL damp location



14" Twist and Lock

(2) 60W A19 max. / Medium Base
Dimensions: Width 14", Height 5¹/₂"
60-287 Textured White / Alabaster Glass
CUL damp location



15" Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 15¹/₄", Height 6"
60-223 Textured White / Alabaster Glass
CUL damp location



17" Twist and Lock

(3) 60W A19 max. / Medium Base
Dimensions: Width 17", Height 6"
60-288 Textured White / Alabaster Glass
CUL damp location

Textured White with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



Hanging Dome

(1) 100W A19 max. / Medium Base
Dimensions: Width 16", Height 11½", Chain 48", Wire 12'
60-393 Textured White / Alabaster Glass
Accessories:
25-1072 3' Section of matching chain



Pendant Bell

(1) 100W A19 max. / Medium Base
Dimensions: Width 9¾", Height 20½", Chain 48", Wire 12'
60-397 Textured White / Alabaster Glass
Accessories:
25-1072 3' Section of matching chain



12" Tri-Clip Flush Dome

(1) 60W A19 max. / Medium Base
Dimensions: Width 12½", Height 4"
60-276 Textured White / Alabaster Glass

16" Tri-Clip Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 16⅛", Height 5"
60-277 Textured White / Alabaster Glass



Empire Mini Pendant

with hang-straight canopy
(1) 100W A19 max. / Medium Base
Dimensions: Width 7", Height 51" Adjustable, Wire 12'
60-368 Textured White / Alabaster Glass
Accessories:
Additional Stem Lengths
25-2053 (6"), **25-2026** (12")



Ballerina Four Light 30" Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"

60-334 Textured White / Alabaster Glass



Ballerina Three Light 24" Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"

60-333 Textured White / Alabaster Glass



Ballerina Five Light 36" Vanity

(5) 100W A19 max. / Medium Base

Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"

60-335 Textured White / Alabaster Glass



Ballerina Two Light 18" Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"

60-332 Textured White / Alabaster Glass



Ballerina Seven Light 48" Vanity

(7) 100W A19 max. / Medium Base

Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"

60-294 Textured White / Alabaster Glass

Textured White with
Alabaster Glass Shades

INTERIOR HOME PACKAGE



Empire Two Light Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"

60-353 Textured White / Alabaster Glass



Empire Three Light Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"

60-354 Textured White / Alabaster Glass



Empire One Light Vanity

(1) 100W A19 max. / Medium Base

Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"

60-352 Textured White / Alabaster Glass



Empire Four Light Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"

60-355 Textured White / Alabaster Glass



24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base
 Dimensions: Width 24", Height 4¾",
 Extension 2" (less lamp)
60-313 Textured White



36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base
 Dimensions: Width 36", Height 4¾",
 Extension 2" (less lamp)
60-314 Textured White



18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base
 Dimensions: Width 18", Height 4¾",
 Extension 2" (less lamp)
60-312 Textured White



48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base
 Dimensions: Width 48", Height 4¾",
 Extension 2" (less lamp)
60-315 Textured White

CHANDELIERS



Five Light Chandelier

(5) 60W B Type max. / Candelabra Base
 Dimensions: Width 18", Height 13", Chain 36", Wire 12'
60-1298 Brushed Nickel
76-280 Polished Brass
 Accessories:
25-1069 3' Section of Brushed Nickel chain
25-1066 3' Section of Polished Brass chain



Five Light Chandelier

(5) 60W A19 max. / Medium Base
 Dimensions: Width 23", Height 13 1/8", Chain 36", Wire 12'
60-1291 Old Bronze / Alabaster Glass
60-1290 Brushed Nickel / Alabaster Glass
 Accessories:
25-1067 3' Section of Old Bronze chain
25-1069 3' Section of Brushed Nickel chain



Five Light Chandelier

(5) 60W A19 max. / Medium Base
 Dimensions: Width 22", Height 18", Chain 36", Wire 12'
76-693 Textured White / Frosted Ribbed Glass
76-695 Brushed Nickel / Frosted Ribbed Glass
76-694 Old Bronze / Frosted Ribbed Glass
 Accessories:
25-1072 3' Section of Textured White chain
25-1069 3' Section of Brushed Nickel chain
25-1067 3' Section of Old Bronze chain



Five Light Chandelier

(5) 60W A19 max. / Medium Base
 Dimensions: Width 22", Height 18", Chain 36", Wire 12'
76-281 Polished Brass / Clear Ribbed Glass
76-444 Brushed Nickel / Clear Ribbed Glass
76-445 Old Bronze / Clear Ribbed Glass
76-449 Textured White / Clear Ribbed Glass
 Accessories:
25-1066 3' Section of Polished Brass chain
25-1069 3' Section of Brushed Nickel chain
25-1067 3' Section of Old Bronze chain
25-1072 3' Section of Textured White chain

PENDANTS



Prismatic Dome

(1) 100W A19 max. / Medium Base
 Dimensions: Width 15", Height 10½", Chain 36", Wire 12'
76-690 Old Bronze / Frosted Ribbed Glass
76-691 Brushed Nickel / Frosted Ribbed Glass
76-692 Textured White / Frosted Ribbed Glass
 Accessories:
25-1069 3' Section of Brushed Nickel chain
25-1067 3' Section of Old Bronze chain
25-1072 3' Section of Textured White chain



Prismatic

(1) 100W A19 max. / Medium Base
76-255 Polished Brass / Clear Ribbed Glass
 Dimensions: Width 12", Height 9", Chain 36", Wire 12'
 Accessories:
25-1066 3' Section of matching chain



Prismatic Dome

(1) 100W A19 max. / Medium Base
 Dimensions: Width 15", Height 10½", Chain 36", Wire 12'
76-282 Polished Brass / Clear Ribbed Glass
76-446 Brushed Nickel / Clear Ribbed Glass
76-447 Old Bronze / Clear Ribbed Glass
76-448 Textured White / Clear Ribbed Glass
 Accessories:
25-1066 3' Section of Polished Brass chain
25-1069 3' Section of Brushed Nickel chain
25-1067 3' Section of Old Bronze chain
25-1072 3' Section of Textured White chain




Three Light Pendant

(3) 60W A19 max. / Medium Base
 Dimensions: Width 22½", Height 17½", Chain 48", Wire 12'
60-371 Old Bronze / Alabaster Glass
60-372 Polished Brass / Alabaster Glass
60-370 Brushed Nickel / Alabaster Glass
60-373 Textured White / Alabaster Glass
 Accessories:
25-1067 3' Section of Old Bronze chain
25-1066 3' Section of Polished Brass chain
25-1069 3' Section of Brushed Nickel chain
25-1072 3' Section of Textured White chain

chandeliers/pendants

PENDANTS



Warehouse Shade

(1) 100W A19 max. / Medium Base

Dimensions: Width 16", Height 8 1/8", Cord 12'

76-661 Brushed Nickel

76-663 Red

76-662 Old Bronze

76-284 Black

76-283 White

76-660 Green



15" Three Light Pendant

(3) 60W A19 max. / Medium Base

Dimensions: Width 15", Height 23", Chain 48", Wire 12'

60-235 Antique Brass / Clear Swirl Glass

60-243 Antique Brass / Frosted Swirl Glass

25-1165 3' Section of matching chain



20" Three Light Pendant

(3) 60W A19 max. / Medium Base

Dimensions: Width 20", Height 23", Chain 48", Wire 12'

60-244 Antique Brass / Frosted Swirl Glass

60-236 Antique Brass / Clear Swirl Glass

Accessories:

25-1165 3' Section of matching chain

CLOSE TO CEILING

CUL listed for damp location



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/8", Height 12", 12' wire
60-240 Antique Brass / Frosted Swirl Glass

13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 13 1/8", Height 14", 12' wire
60-241 Antique Brass / Frosted Swirl Glass

15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15 1/4", Height 15 1/2", 12' wire
60-242 Antique Brass / Frosted Swirl Glass

Accessories:

- 25-1405** 3' Pendant conversion kit for all above
- 25-1165** 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/8", Height 12", 12' wire
60-232 Antique Brass / Clear Swirl Glass

13" Semi-Flush Convertible to Pendant

(2) 60W A19 max. / Medium Base
Dimensions: Width 13 1/4", Height 14", 12' wire
60-233 Antique Brass / Clear Swirl Glass

15" Semi-Flush Convertible to Pendant

(3) 60W A19 max. / Medium Base
Dimensions: Width 15 1/4", Height 15 1/2", 12' wire
60-234 Antique Brass / Clear Swirl Glass

Accessories:

- 25-1405** 3' Pendant conversion kit for all above
- 25-1165** 3' Section of matching chain



11" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/8", Height 4 7/8"
60-237 Antique Brass / Frosted Swirl Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13 1/8", Height 5 3/8"
60-238 Antique Brass / Frosted Swirl Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 15 1/4", Height 6"
60-239 Antique Brass / Frosted Swirl Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/8", Height 4 7/8"
60-229 Antique Brass / Clear Swirl Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base
Dimensions: Width 13 1/8", Height 5 3/8"
60-230 Antique Brass / Clear Swirl Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base
Dimensions: Width 15 1/4", Height 6"
60-231 Antique Brass / Clear Swirl Glass

pendants/close to ceiling

CLOSE TO CEILING



13" Semi-Flush Convertible to Pendant
(2) 60W A19 max. / Medium Base
Dimensions: Width 13", Height 13", 12" wire
76-435 Textured White / Frosted Melon Glass
Accessories:
25-1404 3' Pendant conversion kit
25-1072 3' Section of matching chain



13" Semi-Flush Convertible to Pendant
(2) 60W A19 max. / Medium Base
Dimensions: Width 13", Height 13", 12" wire
76-434 Polished Brass / Frosted Melon Glass
Accessories:
25-1401 3' Pendant conversion kit
25-1066 3' Section of matching chain



13" Semi-Flush Convertible to Pendant
(2) 60W A19 max. / Medium Base
Dimensions: Width 13", Height 13", 12" wire
76-433 Brushed Nickel / Frosted Melon Glass
Accessories:
25-3067 3' Pendant conversion kit
25-1069 3' Section of matching chain



13" Semi-Flush Convertible to Pendant
(2) 60W A19 max. / Medium Base
Dimensions: Width 13", Height 13", 12" wire
76-436 Old Bronze / Frosted Melon Glass
Accessories:
25-1402 3' Pendant conversion kit
25-1067 3' Section of matching chain

CLOSE TO CEILING

CUL listed for damp location



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-125 Textured White / Frosted Melon Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-127 Textured White / Frosted Melon Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-129 Textured White / Frosted Melon Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-124 Polished Brass / Frosted Melon Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-126 Polished Brass / Frosted Melon Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-128 Polished Brass / Frosted Melon Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-243 Brushed Nickel / Frosted Melon Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-244 Brushed Nickel / Frosted Melon Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-245 Brushed Nickel / Frosted Melon Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-246 Old Bronze / Frosted Melon Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-247 Old Bronze / Frosted Melon Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-248 Old Bronze / Frosted Melon Glass

close to ceiling

CLOSE TO CEILING

CUL listed for damp location



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-191 Textured White / Clear Ribbed Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-192 Textured White / Clear Ribbed Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-193 Textured White / Clear Ribbed Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-091 Polished Brass / Clear Ribbed Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-092 Polished Brass / Clear Ribbed Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-093 Polished Brass / Clear Ribbed Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-609 Brushed Nickel / Clear Ribbed Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-610 Brushed Nickel / Clear Ribbed Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-611 Brushed Nickel / Clear Ribbed Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-606 Old Bronze / Clear Ribbed Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-607 Old Bronze / Clear Ribbed Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-608 Old Bronze / Clear Ribbed Glass

CLOSE TO CEILING

CUL listed for damp location



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-131 Textured White / Frosted Ribbed Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-133 Textured White / Frosted Ribbed Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-135 Textured White / Frosted Ribbed Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-130 Polished Brass / Frosted Ribbed Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-132 Polished Brass / Frosted Ribbed Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-134 Polished Brass / Frosted Ribbed Glass



11" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 11 1/4", Height 5"

76-024 Polished Brass / Clear Swirl Glass

13" Flush Dome

(2) 60W A19 max. / Medium Base

Dimensions: Width 13 1/4", Height 5 1/2"

76-025 Polished Brass / Clear Swirl Glass

15" Flush Dome

(3) 60W A19 max. / Medium Base

Dimensions: Width 15 1/4", Height 6"

76-026 Polished Brass / Clear Swirl Glass

close to ceiling

CLOSE TO CEILING

CUL listed for damp location



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
77-059 Polished Brass / White Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
77-061 Polished Brass / White Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"
77-986 Polished Brass / White Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
77-060 White / White Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
77-062 White / White Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"
77-987 White / White Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
77-345 Polished Chrome / White Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
77-346 Polished Chrome / White Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"
77-347 Polished Chrome / White Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
76-600 Old Bronze / White Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
76-602 Old Bronze / White Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"
76-604 Old Bronze / White Glass

CLOSE TO CEILING

CUL listed for damp location



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"

76-601 Brushed Nickel / White Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"

76-603 Brushed Nickel / White Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"

76-605 Brushed Nickel / White Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"

77-921 Antique Brass / White Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"

77-924 Antique Brass / White Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"

77-988 Antique Brass / White Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"

76-612 Textured White / Alabaster Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"

76-613 Textured White / Alabaster Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"

76-614 Textured White / Alabaster Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"

76-672 Polished Brass / Alabaster Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"

76-675 Polished Brass / Alabaster Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"

76-678 Polished Brass / Alabaster Glass

close to ceiling

CLOSE TO CEILING

CUL listed for damp location



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
76-670 Old Bronze / Alabaster Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
76-673 Old Bronze / Alabaster Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"
76-676 Old Bronze / Alabaster Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
76-671 Brushed Nickel / Alabaster Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
76-674 Brushed Nickel / Alabaster Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"
76-677 Brushed Nickel / Alabaster Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
60-2641 Mahogany Bronze / Frosted Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
60-2643 Mahogany Bronze / Frosted Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"
60-2645 Mahogany Bronze / Frosted Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
60-2642 Mahogany Bronze / Champagne Linen Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
60-2644 Mahogany Bronze / Champagne Linen Glass

Large Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 6"
60-2646 Mahogany Bronze / Champagne Linen Glass

CLOSE TO CEILING

CUL listed for damp location



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
76-250 Polished Brass / Clear Ribbed Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
76-252 Polished Brass / Clear Ribbed Glass



Small Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 7 1/2", Height 5"
76-251 White / Clear Ribbed Glass

Medium Mushroom

(2) 60W A19 max. / Medium Base
Dimensions: Width 9 1/2", Height 6"
76-253 White / Clear Ribbed Glass



Small Frosted Grape Mushroom

(1) 60W A19 max. / Medium Base
Dimensions: Width 6", Height 5"
77-123 Polished Brass / Frosted Grape Glass



Clear Bottom Squat Ball

(1) 60W A19 max. / Medium Base
Dimensions: Width 5", Height 5 1/2"
77-122 Polished Brass / Frosted, Clear Bottom Glass



Clear Pineapple

(1) 60W A19 max. / Medium Base
Dimensions: Width 5", Height 5 1/2"
77-125 Polished Brass / Clear Pineapple Glass

close to ceiling

CLOSE TO CEILING

CUL listed for damp location



6" Flush Ball

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 7 1/4"

60-245 Brushed Nickel / White Glass

60-247 Old Bronze / White Glass

77-108 Polished Brass / White Glass

77-110 Polished Chrome / White Glass

77-947 White / White Glass



6" Flush Ball

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 7 1/4"

76-256 Polished Brass / Clear Ribbed Glass

76-257 White / Clear Ribbed Glass



8" Flush Ball

(1) 60W A19 max. / Medium Base

Dimensions: Width 8", Height 9 1/4"

77-109 Polished Brass / White Glass

77-111 Polished Chrome / White Glass

77-948 White / White Glass



6" Flush Ball with Pull Chain Switch

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 7 1/4"

60-295 Polished Brass / White Glass

CLOSE TO CEILING

CUL listed for damp location



Small Flush Drum

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 5"

77-100 Polished Chrome / Crystal & White Glass

Medium Flush Drum

(2) 60W A19 max. / Medium Base

Dimensions: Width 8", Height 6"

77-101 Polished Chrome / Crystal & White Glass

Large Flush Drum

(2) 60W A19 max. / Medium Base

Dimensions: Width 10", Height 7"

77-102 Polished Chrome / Crystal & White Glass



Small Flush Drum

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 5"

77-097 White / Crystal & White Glass

Medium Flush Drum

(2) 60W A19 max. / Medium Base

Dimensions: Width 8", Height 6"

77-098 White / Crystal & White Glass

Large Flush Drum

(2) 60W A19 max. / Medium Base

Dimensions: Width 10", Height 7"

77-099 White / Crystal & White Glass



Small Flush Drum

(1) 60W A19 max. / Medium Base

Dimensions: Width 6", Height 5"

77-342 Polished Chrome / White Glass

Medium Flush Drum

(2) 60W A19 max. / Medium Base

Dimensions: Width 8", Height 6"

77-343 Polished Chrome / White Glass

Large Flush Drum

(2) 60W A19 max. / Medium Base

Dimensions: Width 10", Height 7"

77-344 Polished Chrome / White Glass



CLOSE TO CEILING

CUL listed for damp location



Square Wheat Design / Ruffled Edge

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/4", Height 4 3/4"
76-270 White Holder



Square Floral Design

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/4", Height 4 3/4"
77-126 White Holder



Square White

(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/4", Height 4 3/4"
77-824 White Holder



Square Floral Design

with Pull Chain Switch
(2) 60W A19 max. / Medium Base
Dimensions: Width 11 3/4", Height 4 3/4"
77-392 White Holder

CLOSE TO CEILING

CUL listed for damp location



Round Grape Design

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 4 3/4"
76-268 White Holder



Round White

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 4 3/4"
77-823 White Holder



Round Sunburst Design

(2) 60W A19 max. / Medium Base
Dimensions: Width 12", Height 4 3/4"
76-269 White Holder

close to ceiling

CLOSE TO CEILING

CUL listed for damp location



R20 / PAR20 1 Light Straight Cylinder

(1) 50W R20 / PAR20 Halogen max. / Medium Base

Dimensions: Height 8½", Canopy 5"

76-412 White / Black Baffle



R20 / PAR20 3 Light Straight Cylinder

(3) 50W R20 / PAR20 Halogen max. / Medium Base

Dimensions: Height 8½", Width 14", Canopy 10"

76-416 White / Black Baffle



R30 / PAR30 1 Light Straight Cylinder

(1) 75W R30 / 50W PAR30 Halogen max. / Medium Base

Dimensions: Height 10", Canopy 5"

76-418 White / Black Baffle



R30 / PAR30 3 Light Straight Cylinder

(3) 75W R30 / 50W PAR30 Halogen max. / Medium Base

Dimensions: Height 10", Width 18", Canopy 10"

76-422 White / Black Baffle

VANITY AND WALL

CUL listed for damp location



7" "U" Channel Glass

(1) 60W A19 max. / Medium Base

Dimensions: Width 4 1/2", Height 7 1/2", Extension 4 1/4"

76-273 White / White Diamond Glass

77-086 White / White Glass

77-989 White / White Glass w/ Bottom Turn Switch



Crystal Bottom Bath Shade

(1) 60W A19 max. / Medium Base

Dimensions: Width 4 3/4", Height 4 3/4",
Extension 6 3/4"

77-121 Chrome / White Glass,
Crystal Bottom, with Convenience Outlet



14" "U" Channel Glass

(2) 60W A19 max. / Medium Base

Dimensions: Width 14", Height 4 3/4", Extension 4 1/4"

76-276 White / White Diamond Glass

77-087 White / White Glass

77-990 White / White Glass w/ Convenience Outlet



Frosted Grape Shade

(1) 60W A19 max. / Medium Base

Dimensions: Width 4 1/2", Height 7 3/4",
Extension 4 7/8"

77-120 Polished Brass / Frosted Glass,
with On-Off Switch



24" "U" Channel Glass

(4) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 4 3/4", Extension 4 1/4"

76-277 White / White Diamond Glass

77-088 White / White Glass

77-991 White / White Glass w/ Convenience Outlet

close to ceiling/vanity/wall

VANITY

CUL listed for damp location



Ballerina Two Light 18" Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"

60-316 Polished Chrome / Alabaster Glass

Ballerina Three Light 24" Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"

60-317 Polished Chrome / Alabaster Glass

Ballerina Four Light 30" Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"

60-318 Polished Chrome / Alabaster Glass

Ballerina Five Light 36" Vanity

(5) 100W A19 max. / Medium Base

Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"

60-319 Polished Chrome / Alabaster Glass

Ballerina Seven Light 48" Vanity

(7) 100W A19 max. / Medium Base

Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"

60-290 Polished Chrome / Alabaster Glass

Empire One Light Vanity

(1) 100W A19 max. / Medium Base

Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"

60-336 Polished Chrome / Alabaster Glass

Empire Two Light Vanity

(2) 100W A19 max. / Medium Base

Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"

60-337 Polished Chrome / Alabaster Glass

Empire Three Light Vanity

(3) 100W A19 max. / Medium Base

Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"

60-338 Polished Chrome / Alabaster Glass

Empire Four Light Vanity

(4) 100W A19 max. / Medium Base

Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"

60-339 Polished Chrome / Alabaster Glass

VANITY

CUL listed for damp location



18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base

Dimensions: Width 18", Height 4 3/4",
Extension 2" (less lamp)

60-296 Polished Chrome

24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base

Dimensions: Width 24", Height 4 3/4",
Extension 2" (less lamp)

60-297 Polished Chrome

36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base

Dimensions: Width 36", Height 4 3/4",
Extension 2" (less lamp)

60-298 Polished Chrome

48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base

Dimensions: Width 48", Height 4 3/4",
Extension 2" (less lamp)

60-299 Polished Chrome

18" Three Light Vanity Strip

(3) 100W Type G max. / Medium Base

Dimensions: Width 18", Height 4 3/4",
Extension 2" (less lamp)

77-188 Polished Brass

77-192 Polished Chrome

24" Four Light Vanity Strip

(4) 100W Type G max. / Medium Base

Dimensions: Width 24", Height 4 3/4",
Extension 2" (less lamp)

77-189 Polished Brass

77-193 Polished Chrome

30" Five Light Vanity Strip

(5) 100W Type G max. / Medium Base

Dimensions: Width 30", Height 4 3/4",
Extension 2" (less lamp)

77-196 Polished Chrome

36" Six Light Vanity Strip

(6) 100W Type G max. / Medium Base

Dimensions: Width 36", Height 4 3/4",
Extension 2" (less lamp)

77-190 Polished Brass

77-194 Polished Chrome

48" Eight Light Vanity Strip

(8) 100W Type G max. / Medium Base

Dimensions: Width 48", Height 4 3/4",
Extension 2" (less lamp)


77-191 Polished Brass

77-195 Polished Chrome

vanity

A simple design with so many possibilities. That's the best way to describe Nuvo's wall and ceiling socket fixtures. Line them up, or group them on ceilings or walls to create simple, yet dramatic lighting solutions that show off today's most popular decorative lamp styles.

CEILING / WALL



Style Socket

(1) 60W max. / Medium Base

Dimensions: Diameter 5", Extension 2³/₈" (less lamp)

60-4801 Brushed Nickel

60-4802 Polished Nickel

60-4803 White

60-4804 Dark Bronze

CUL listed for damp location



The 60-4802 (Polished Nickel) shown with assorted optional Satco lamps

Small Plumen



Large Plumen



Silver Crown



Vintage A19



Vintage Cage Style



G25 LED Globe



G25 CFL Globe



G25 White Globe



G40 White Globe



G40 Clear Globe



G25 Clear Globe



ceiling / wall

4 FT TRACK LIGHTING KITS



PAR30 Gimbal Ring
 (3) PAR30 (Shortneck) 75W max. / Medium Base
 TK316 White



TK317 Black
 TK343 Brushed Nickel
 TK362 Russet Bronze



R30 Straight Cylinder
 (3) R30/PAR30 (Longneck) 75W max. / Medium Base
 TK318 White



TK319 Black
 TK341 Brushed Nickel



R30 Step Cylinder
 (3) R30/PAR30 (Longneck) 75W max. / Medium Base
 TK320 White



TK321 Black
 TK340 Brushed Nickel
 TK361 Russet Bronze



R30 Bullet Cylinder
 (3) R30/PAR30 (Longneck) 75W max. / Medium Base
 TK322 White



TK323 Black
 TK342 Brushed Nickel

SWIVEL TRACK LIGHTING KITS



CFL R30 Bullet Swivel
 (4) R30 15W / GU24 Base (Included)
 Dimensions: Length 4', Extension 11"
TK381* Russet Bronze



CFL R30 Bullet Swivel
 (4) R30 15W / GU24 Base (Included)
 Dimensions: Length 4', Extension 11"
TK382* Brushed Nickel



Energy Saving
 Fixtures Include
 GU24 Base CFLs.



MR16 Halogen Swivel
 (4) 50W MR16 / GU10 base 120V max.
 Dimensions: Length 4', Extension 8"
TK383 Russet Bronze



MR16 Halogen Swivel
 (4) 50W MR16 / GU10 base 120V max.
 Dimensions: Length 4', Extension 8"
TK384 Brushed Nickel

4 Ft. Linear Track Kits (opposite page) Include:

- (1) Four foot track
- (3) Track lighting heads
- (1) Floating power feed canopy kit
- All necessary mounting hardware
- Four color display carton



Linear track kits supplied
 with floating canopy kit

track lighting kits

4 FT TRACK LIGHTING KITS



MR16 Square

(3) 50W MR16 / GU10 base 120V max.
TK345 White



TK346 Black
TK347 Brushed Nickel



MR16 Round Back

(3) 50W MR16 / GU10 base 120V max.
TK348 White



TK349 Black
TK354 Brushed Nickel



MR16 Gimbal Ring

(3) 50W MR16 / GU10 base 120V max.
TK355 White



TK352 Black
TK353 Brushed Nickel

4 Ft. Linear Track Kits Include:

- (1) Four foot track
- (3) Track lighting heads
- (1) Floating power feed canopy kit
- All necessary mounting hardware
- Four color display carton



Linear track kits supplied with floating canopy kit

12V 4 FT TRACK LIGHTING KITS



12V MR16 Square

(3) 50W MR16 / GX5.3 base 12V max.
TK310 White



TK311 Black



12V MR16 Round Back

(3) 50W MR16 / GX5.3 base 12V max.
TK312 White



TK313 Black



12V MR16 Gimbal Ring

(3) 50W MR16 / GX5.3 base 12V max.
TK314 White



TK315 Black

track lighting kits

4 Ft. Linear Track Kits Include:

- (1) Four foot track
- (3) Track lighting heads
- (1) Floating power feed canopy kit
- All necessary mounting hardware
- Four color display carton



Linear track kits supplied with floating canopy kit

TRACK HEADS

R20 Step Cylinder

Dimensions: Height 5 1/4", Width 3 1/2", Extension 7 1/2"

(1) R20/PAR20 50W max. / Medium Base

TH204 White

TH205 Black

TH303 Brushed Nickel

TH341 Russet Bronze (shown)



R20 Straight Cylinder

Dimensions: Height 6 1/2", Width 4 1/4", Extension 9 1/2"

(1) R20/PAR20 50W max. / Medium Base

TH200 White

TH201 Black

TH307 Brushed Nickel (shown)

TH343 Russet Bronze



R20 Bullet Cylinder

Dimensions: Height 6", Width 3 1/2", Extension 8"

(1) R20/PAR20 50W max. / Medium Base

TH208 White

TH209 Black (shown)

TH305 Brushed Nickel

TH345 Russet Bronze



TRACK HEADS

R30 Step Cylinder

Dimensions: Height 6 1/2", Width 4 1/2", Extension 8 1/2"
(1) R30/PAR30 75W max. (Long Neck) / Medium Base

TH206 White

TH207 Black

TH304 Brushed Nickel (shown)

TH342 Russet Bronze



R30 Straight Cylinder

Dimensions: Height 7", Width 4 1/2", Extension 9 1/2"
(1) R30/PAR30 75W max. (Long Neck) / Medium Base

TH202 White

TH203 Black

TH308 Brushed Nickel

TH344 Russet Bronze (shown)



R30 Bullet Cylinder

Dimensions: Height 7", Width 4 1/2", Extension 9 1/2"
(1) R30/PAR30 75W max. (Long Neck) / Medium Base

TH210 White (shown)

TH211 Black

TH306 Brushed Nickel

TH346 Russet Bronze



track heads

TRACK HEADS

PAR20 Short Bullet Cylinder

Dimensions: Height 4 1/2",
Width 3 1/2", Extension 7"

(1) PAR20 50W max. /
Medium Base

TH216 White (shown)

TH217 Black



PAR30 Short Bullet Cylinder

Dimensions: Height 5 1/8",
Width 4 1/2", Extension 8"

(1) PAR30 75W max. /
(short neck) Medium Base

TH218 White

TH219 Black (shown)



PAR20 Gimbal Ring

Dimensions: Height 4 1/2",
Width 2 3/4", Extension 6 3/4"

(1) PAR20 50W max. /
Medium Base

TH220 White

TH221 Black

TH300 Brushed Nickel (shown)

TH347 Russet Bronze



PAR30 Gimbal Ring

Dimensions: Height 4 3/4",
Width 4", Extension 10 1/2"

(1) PAR30 75W max. /
(short neck) Medium Base

TH222 White (shown)

TH223 Black

TH301 Brushed Nickel

TH348 Russet Bronze



PAR38 Gimbal Ring

Dimensions: Height 6 1/4",
Width 5", Extension 10 1/2"

(1) PAR20 50W max. /
Medium Base

TH224 White

TH225 Black (shown)

TH302 Brushed Nickel

TH349 Russet Bronze



PAR30 Euro Style

Dimensions: Height 7 1/2",
Width 4 1/2", Extension 8 1/2"

(1) PAR30 75W max. /
(short neck) Medium Base

TH332 White

TH333 Black

TH331 Brushed Nickel
(shown)



TRACK HEADS

R40 Step Cylinder

Dimensions: Height 8",
Width 5 1/2", Extension 11"

(1) 150W BR40/PAR38/
BR38 max. / Medium Base

TH281 White

TH282 Black (shown)



R40 Straight Cylinder

Dimensions: Height 8",
Width 5 1/2", Extension 12"

(1) 150W BR40/PAR38/
BR38 max. / Medium Base

TH283 White (shown)

TH284 Black



Universal Holder

Dimensions: Height 4 3/4",
Width 2", Extension 7" (without lamp)

(1) R20/BR30/BR40/PAR20 /PAR30/
PAR38 150W.max. / Medium Base

TH226 White

TH227 Black

TH324 Brushed Nickel (shown)



Mini Universal Holder

Dimensions: Height 4 3/4", Width 2",
Extension 7" (without lamp)

(1) R20/BR30/BR40/PAR20 /PAR30/
PAR38 150W.max. / Medium Base

TH279 White

TH280 Black (shown)



track heads

Power Flood with Barndoor

Dimensions: Height 2 3/4",
Width 5", Extension 7"

(1) 150W J Type 78MM
(Short) max.

TH228 White

TH229 Black (shown)



12V TRACK HEADS

12V MR16 Square

Dimensions: Height 3 1/4", Width 2 1/4", Extension 6 1/2"

(1) 50W MR16 12V max. / GX5.3 Base

TH232 White (shown)

TH233 Black

TH310 Brushed Nickel



12V MR16 Round

Dimensions: Height 3 1/4", Width 2 1/4", Extension 6 1/2"

(1) 50W MR16 12V max. / GX5.3 Base

TH234 White

TH235 Black (shown)

TH309 Brushed Nickel



12V MR16 Roundback

Dimensions: Height 3 1/4", Width 2 1/4", Extension 6 1/2"

(1) 50W MR16 12V max. / GX5.3 Base

TH236 White

TH237 Black

TH327 Brushed Nickel (shown)



12V MR16 Gimbal Ring

Dimensions: Height 2 1/4", Width 2", Extension 6 1/2"

(1) 50W MR16 12V max. / GX5.3 Base

TH238 White

TH239 Black

TH311 Brushed Nickel (shown)



12V TRACK HEADS

12V MR16 Cast Ring

Dimensions: Height 4", Width 2 1/4", Extension 6 1/2"

(1) 50W MR16 12V max. / GX5.3 Base

TH259 White

TH260 Black

TH328 Brushed Nickel (shown)



12V MR11 Mini Round

Dimensions: Height 3 1/4", Width 2 1/4", Extension 6 1/2"

(1) 50W MR16 12V max. / GX5.3 Base

TH267 White (shown)

TH268 Black



12V MR11 Mini Square

Dimensions: Height 2 1/4", Width 1 1/2", Extension 5 1/2"

(1) 50W MR16 12V max. / GX5.3 Base

TH269 White

TH270 Black (shown)



12V PAR36 Gimbal Ring

Dimensions: Height 3", Width 4 1/4", Extension 7"

(1) 50W PAR36 12V max. / Screw Terminal Base

TH271 White (shown)

TH272 Black



track heads

TRACK HEADS

MR16 Square

Dimensions: Height 3 1/4", Width 2 1/4", Extension 6 1/2"

(1) 50W MR16 / GU10 base 120V max.

TH312 White

TH313 Black (shown)

TH314 Brushed Nickel



MR16 Roundback

Dimensions: Height 3 1/4", Width 2 1/4", Extension 6 1/2"

(1) 50W MR16 / GU10 base 120V max.

TH315 White

TH316 Black

TH317 Brushed Nickel (shown)

TH351 Russet Bronze



MR16 Gimbal Ring

Dimensions: Height 2 1/4", Width 2", Extension 4 1/2"

(1) 50W MR16 / GU10 base 120V max.

TH321 White

TH322 Black

TH323 Brushed Nickel

TH352 Russet Bronze (shown)



CFL TRACK HEADS

CFL R30 Step Cylinder

Dimensions: Height 5", Width 4 1/2", Extension 7"

(1) R30 15W / GU24 Base (Included)

TH355* White (shown)

TH356* Black

TH357* Brushed Nickel

TH358* Russet Bronze



CFL R30 Straight Cylinder

Dimensions: Height 5 1/2", Width 4 1/2", Extension 8"

(1) R30 15W / GU24 Base (Included)

TH361* White

TH362* Black

TH363* Brushed Nickel (shown)

TH364* Russet Bronze



CFL R30 Bullet Cylinder

Dimensions: Height 5 1/2", Width 4 1/2", Extension 8"

(1) R30 15W / GU24 Base (Included)

TH365* White

TH366* Black

TH367* Brushed Nickel

TH368* Russet Bronze (shown)



track heads



Energy Saving
Track Heads Include
GU24 Base CFLs.

ARCHITECTURAL TRACK HEADS

Metal Halide

Dimensions: Height 6 1/2", Width 4 1/2", Extension 8 1/2"

(1) T4 39W/ MH / G12 Base

TH381 White

TH382 Black (shown)



Metal Halide

Dimensions: Height 6 1/2", Width 4 1/2", Extension 8 1/2"

(1) MR16 20W/ CMH / GX10 Base

TH383 White (shown)

TH384 Black



Metal Halide

Dimensions: Height 6 1/2", Width 4 1/2", Extension 8 1/2"

(1) PAR30 (long neck) 70W / MH / Medium base

TH385 White

TH386 Black (shown)



TRACK ACCESSORIES

Tracks

All tracks include two dead end caps and all mounting hardware
 Dimensions: Height 5/8", Width 1 5/16" (length and color options below)

Size	White	Black	Brushed Nickel	Russet Bronze
2 FT	TR118	TR119	TR126	TR131
4 FT	TR120	TR121	TR127	TR132
6 FT	TR124	TR125	TR128	TR133
8 FT	TR122	TR123	TR129	TR134



Extensions

Lowers track heads to desired height

Size	White	Black
18 IN	TP159	TP163
24 IN	TP160	TP164
36 IN	TP161	TP165
48 IN	TP162	TP166



Line Voltage (120V) Monopoint Adapters

Individually mounts a single track head to a junction box

- TP142 White
- TP143 Black



Low Voltage (12V) Monopoint Adapters

Offset monopoint for low voltage track heads

- TP176 White
- TP177 Black



24" Pendant Suspension Kit

Kit Includes: canopy, stem, support and power feed accessories

- TP178 White
- TP179 Black



White Baffle

Replaces standard black baffle

- TP180 White, for R20 or PAR20 round cylinders
- TP181 White, for R30, BR30 or PAR 30 round cylinders



track heads / accessories

TRACK POWER FEEDS

Floating Canopy

Electrifies the track anywhere along the length of the run

TP154 White

TP155 Black

TP202 Brown



Self Grounding
3 Conductor System



Conduit Live End

Electrifies the track from the end of the run to a conduit pipe

TP169 White

TP170 Black

TP203 Brown



Live End and Canopy

Electrifies the track from the end of the run

TP152 White

TP153 Black

TP204 Brown



"T" Connector

Connects three tracks together in a "T" shape pattern

TP148 White

TP149 Black

TP207 Brown



Inline Feed

Connects tracks in a straight run and supplies power

TP171 White

TP172 Black

TP211 Brown



TRACK CONNECTORS

Mini Straight Connector

Connects tracks in a straight run

TP144 White

TP145 Black

TP205 Brown



"L" Connector

Connects tracks at a 90° angle

TP146 White

TP147 Black

TP208 Brown



"X" Connector

Connects four tracks together in a n"X" shape pattern

TP150 White

TP151 Black

TP206 Brown



Flexible Connector

Variable angle connector

TP167 White

TP168 Black

TP209 Brown



Live End Cord Kit

Electrifies the track from the end of the run, supplied with 15' of two conductor wire and line switch

TP156 White

TP157 Black

TP201 Brown



Pendant Track Adapter

Connects pendant (cord) to track

• Supports up to 10 lbs max

• For SVT 18/3 wire

TP231 White

TP232 Black

TP233 Brown



track feeds / connectors

Impressive designs.
Measurable savings.



The art of efficiency.

Saving energy is something that's been on the mind of every builder, large or small, for many years. And there are many ways to save; the right appliances, proper insulation, high-quality doors and windows, air-tight construction techniques and, of course, choosing the right lighting. And it's not just about rules and regulations—it's the right thing to do. But when you choose lighting, will you have to sacrifice design? We don't think so.

Nuvo has created a beautifully designed collection of fixtures, most of which are ENERGY STAR® certified and sure to add impact to any room while saving energy at the same time.

Family collections, vanity and ceiling variations and home packages are all designed to save energy in virtually any living space at the flick of a switch. The next 40 or so pages will convince you that energy efficiency and beauty can go hand in hand.



efficiency

Dupont is an affordable collection which offers quality and style. Fine details such as rich finishes, finely crafted satin white glassware and great attention to construction are evident throughout.

DUPONT ES



Two Tier – Nine Light Chandelier

*(9) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 27 1/2", Height 23 1/2", Chain 72", Wire 12'

60-1903 Brushed Nickel / Satin White Glass

Accessories:

25-1069 3' Section of matching chain





Three Light Chandelier

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 17", Height 13½", Chain 48", Wire 12'
60-1901 Brushed Nickel / Satin White Glass
Convertible – Arms up or Down
Accessories:
25-1069 3' Section of matching chain



Small Flush Dome

* (1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11", Height 7"
60-1904 Brushed Nickel / Satin White Glass
CUL damp location



Mini Pendant

* (1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 42" Adjustable, Wire 12'
60-1911 Brushed Nickel / Satin White Glass
Accessories:
Additional Stem Lengths
25-2047 (6"), **25-2021** (12")



Medium Flush Dome

* (2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13", Height 7"
60-1905 Brushed Nickel / Satin White Glass
CUL damp location



Semi-Flush Dome

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 16", Height 15½", Wire 12'
60-1907 Brushed Nickel / Satin White Glass
Convertible to pendant
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



Large Flush Dome

* (2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 7¾"
60-1906 Brushed Nickel / Satin White Glass
CUL damp location



DUPONT ES



Five Light Chandelier

*(5) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 22", Height 15³/₄", Chain 48", Wire 12'

60-1902 Brushed Nickel / Satin White Glass

Convertible – Arms up or Down

Accessories:

25-1069 3' Section of matching chain





Three Light Pendant

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 16", Height 20", Chain 48", Wire 12"
60-1908 Brushed Nickel / Satin White Glass
Accessories:
25-1069 3' Section of matching chain



Two Light Vanity

* (2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13", Height 8", Extension 7 3/4"
60-1913 Brushed Nickel / Satin White Glass



Hanging Dome

(1) 15W CFL Globe / GU24 base / 2700K Included
Dimensions: Width 16", Height 10 1/2", Chain 48", Wire 12"
60-1909 Brushed Nickel / Satin White Glass
Accessories:
25-1069 3' Section of matching chain



Three Light Vanity

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24", Height 8", Extension 7 3/4"
60-1914 Brushed Nickel / Satin White Glass



One Light Vanity

* (1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 8", Extension 8 1/2"
60-1912 Brushed Nickel / Satin White Glass



Four Light Vanity

* (4) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 30", Height 8", Extension 7 3/4"
60-1915 Brushed Nickel / Satin White Glass



DUPONT ES



Two Tier – Nine Light Chandelier

*(9) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 27 1/2", Height 23 1/2", Chain 72", Wire 12'

60-1923 Dark Chocolate Bronze / Satin White Glass

Accessories:

25-3024 3' Section of matching chain





Three Light Chandelier

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 17", Height 13½", Chain 48", Wire 12'
60-1921 Dark Chocolate Bronze / Satin White Glass
Convertible – Arms up or Down

Accessories:

25-3024 3' Section of matching chain



Small Flush Dome

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11", Height 7"

60-1924 Dark Chocolate Bronze / Satin White Glass
CUL damp location



Mini Pendant

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 42" Adjustable, Wire 12'
60-1931 Dark Chocolate Bronze / Satin White Glass

Accessories:

Additional Stem Lengths

25-4007 (6"), **25-4008** (12")



Medium Flush Dome

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13", Height 7"

60-1925 Dark Chocolate Bronze / Satin White Glass
CUL damp location



Semi-Flush Dome

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 16", Height 15½", Wire 12'
60-1927 Dark Chocolate Bronze / Satin White Glass

Convertible to pendant

Accessories:

25-3073 Pendant conversion kit

25-3024 3' Section of matching chain



Large Flush Dome

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 7¾"

60-1926 Dark Chocolate Bronze / Satin White Glass
CUL damp location



DUPONT ES



Five Light Chandelier

*(5) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 22", Height 15³/₄", Chain 48", Wire 12'

60-1922 Dark Chocolate Bronze / Satin White Glass

Convertible – Arms up or Down

Accessories:

25-3024 3' Section of matching chain





Three Light Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 16", Height 20", Chain 48", Wire 12"
60-1928 Dark Chocolate Bronze / Satin White Glass
Accessories:
25-3024 3' Section of matching chain



Two Light Vanity

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13", Height 8", Extension 7 3/4"
60-1933 Dark Chocolate Bronze / Satin White Glass



Hanging Dome

(1) 15W CFL Globe / GU24 base / 2700K Included
Dimensions: Width 16", Height 10 1/2", Chain 48", Wire 12"
60-1929 Dark Chocolate Bronze / Satin White Glass
Accessories:
25-3024 3' Section of matching chain



Three Light Vanity

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24", Height 8", Extension 7 3/4"
60-1934 Dark Chocolate Bronze / Satin White Glass



One Light Vanity

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 8", Extension 8 1/2"
60-1932 Dark Chocolate Bronze / Satin White Glass



Four Light Vanity

*(4) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 30", Height 8", Extension 7 3/4"
60-1935 Dark Chocolate Bronze / Satin White Glass



Mahogany Bronze
with Champagne Linen
Washed Glass Shades

Deep rich Mahogany Bronze is accented
by Champagne Linen glass in this
complete product grouping which
offers a fixture for every application.

INTERIOR HOME ES PACKAGE



Two Tier - Nine Light Empire Chandelier

*(9) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-3131 Mahogany Bronze / Champagne Glass

Accessories:

25-2081 3' Section of matching chain





Five Light Ballerina Chandelier

*(5) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24", Height 18", Chain 48", Wire 12'
60-3101 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain



Five Light Gotham Chandelier

*(5) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'
60-3103 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain



Three Light Ballerina Chandelier

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20", Height 17", Chain 48", Wire 12'
60-3102 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain



Three Light Gotham Chandelier

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'
60-3104 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain



Six Light Empire Chandelier

*(6) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 26", Height 14", Chain 48", Wire 12'
60-3129 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain

Mahogany Bronze
with Champagne Linen
Washed Glass Shades

INTERIOR HOME ES PACKAGE



20" Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-3113 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain



15" Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-3112 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-3111 Mahogany Bronze / Champagne Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-3109 Mahogany Bronze / Champagne Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-3108 Mahogany Bronze / Champagne Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain





11" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11 3/8", Height 4 7/8"
60-3105 Mahogany Bronze / Champagne Glass
CUL damp location



12" Twist and Lock

*(1) 18WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11 1/2", Height 4 1/2"
60-3135 Mahogany Bronze / Champagne Glass
CUL damp location



13" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13 1/4", Height 5 3/8"
60-3106 Mahogany Bronze / Champagne Glass
CUL damp location



14" Twist and Lock

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 14", Height 5 1/2"
60-3136 Mahogany Bronze / Champagne Glass
CUL damp location



15" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15 1/4", Height 6"
60-3107 Mahogany Bronze / Champagne Glass
CUL damp location



17" Twist and Lock

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 17", Height 6"
60-3137 Mahogany Bronze / Champagne Glass
CUL damp location

Mahogany Bronze
with Champagne Linen
Washed Glass Shades

INTERIOR HOME ES PACKAGE



Hanging Dome

(1) 15W CFL Globe / GU24 base / 2700K Included
Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'
60-3133 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain



Pendant Bell

*(1) 18W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'
60-3134 Mahogany Bronze / Champagne Glass
Accessories:
25-2081 3' Section of matching chain



6" Flush Ball

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 7 1/4"
60-3114 Mahogany Bronze / Champagne Glass
CUL damp location



Empire Mini Pendant

with hang-straight canopy
*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7", Height 51" Adjustable, Wire 12'
60-3132 Mahogany Bronze / Champagne Glass
Accessories:
Additional Stem Lengths
25-2078 (6"), **25-2079** (12")





Ballerina Four Light 30" Vanity

*(4) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"
60-3123 Mahogany Bronze / Champagne Glass



Ballerina Three Light 24" Vanity

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"
60-3122 Mahogany Bronze / Champagne Glass



Ballerina Five Light 36" Vanity

*(5) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"
60-3124 Mahogany Bronze / Champagne Glass



Ballerina Two Light 18" Vanity

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"
60-3121 Mahogany Bronze / Champagne Glass



Ballerina Seven Light 48" Vanity

*(7) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"
60-3115 Mahogany Bronze / Champagne Glass

interior home es package

Mahogany Bronze
with Champagne Linen
Washed Glass Shades

INTERIOR HOME ES PACKAGE



Empire Two Light Vanity

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-3126 Mahogany Bronze / Champagne Glass



Empire Three Light Vanity

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-3127 Mahogany Bronze / Champagne Glass



Empire One Light Vanity

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-3125 Mahogany Bronze / Champagne Glass



Empire Four Light Vanity

*(4) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-3128 Mahogany Bronze / Champagne Glass





24" Four Light Vanity Strip

†(4) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 24", Height 4 3/4",
Extension 6 1/4" (with lamp)

60-3347 Mahogany Bronze



36" Six Light Vanity Strip

†(6) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 36", Height 4 3/4",
Extension 6 1/4" (with lamp)

60-3348 Mahogany Bronze



18" Three Light Vanity Strip

†(3) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 18", Height 4 3/4",
Extension 6 1/4" (with lamp)

60-3346 Mahogany Bronze



48" Eight Light Vanity Strip

†(8) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 48", Height 4 3/4",
Extension 6 1/4" (with lamp)

60-3349 Mahogany Bronze

interior home es package

Vanity fixtures CUL listed for damp location and glass up or down installation.



All Energy Saving
Fixtures Include
GU24 Base CFLs

Mahogany Bronze with Frosted White Glass Shades

Deep rich Mahogany Bronze is accented by Frosted White glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME ES PACKAGE



Two Tier - Nine Light Empire Chandelier

*(9) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-3361 Mahogany Bronze / Frosted Glass

Accessories:

25-2081 3' Section of matching chain





Five Light Ballerina Chandelier

* (5) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 24", Height 18", Chain 48", Wire 12'
60-3331 Mahogany Bronze / Frosted Glass
 Accessories:
25-2081 3' Section of matching chain



Five Light Gotham Chandelier

* (5) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'
60-3333 Mahogany Bronze / Frosted Glass
 Accessories:
25-2081 3' Section of matching chain



Three Light Ballerina Chandelier

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 20", Height 17", Chain 48", Wire 12'
60-3332 Mahogany Bronze / Frosted Glass
 Accessories:
25-2081 3' Section of matching chain



Three Light Gotham Chandelier

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'
60-3334 Mahogany Bronze / Frosted Glass
 Accessories:
25-2081 3' Section of matching chain



Six Light Empire Chandelier

* (6) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 26", Height 14", Chain 48", Wire 12'
60-3359 Mahogany Bronze / Frosted Glass
 Accessories:
25-2081 3' Section of matching chain

Mahogany Bronze with
Frosted White Glass Shades

INTERIOR HOME ES PACKAGE



20" Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-3343 Mahogany Bronze / Frosted Glass
Accessories:
25-2081 3' Section of matching chain



15" Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-3342 Mahogany Bronze / Frosted Glass
Accessories:
25-2081 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-3341 Mahogany Bronze / Frosted Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-3339 Mahogany Bronze / Frosted Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-3338 Mahogany Bronze / Frosted Glass
Accessories:
25-2082 Pendant conversion kit
25-2081 3' Section of matching chain





11" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11 3/8", Height 4 7/8"
60-3335 Mahogany Bronze / Frosted Glass
CUL damp location



12" Twist and Lock

*(1) 18WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11 1/2", Height 4 1/2"
60-3365 Mahogany Bronze / Frosted Glass
CUL damp location



13" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13 1/4", Height 5 3/8"
60-3336 Mahogany Bronze / Frosted Glass
CUL damp location



14" Twist and Lock

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 14", Height 5 1/2"
60-3366 Mahogany Bronze / Frosted Glass
CUL damp location



15" Flush Dome

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15 1/4", Height 6"
60-3337 Mahogany Bronze / Frosted Glass
CUL damp location



17" Twist and Lock

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 17", Height 6"
60-3367 Mahogany Bronze / Frosted Glass
CUL damp location

Mahogany Bronze with
Frosted White Glass Shades

INTERIOR HOME ES PACKAGE



Hanging Dome

(1) 15W CFL Globe / GU24 base / 2700K Included
Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'
60-3363 Mahogany Bronze / Frosted Glass
Accessories:
25-2081 3' Section of matching chain



Pendant Bell

*(1) 18W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'
60-3364 Mahogany Bronze / Frosted Glass
Accessories:
25-2081 3' Section of matching chain



6" Flush Ball

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 7 1/4"
60-3344 Mahogany Bronze / Frosted Glass
CUL damp location



Empire Mini Pendant

with hang-straight canopy
*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7", Height 51" Adjustable, Wire 12'
60-3362 Mahogany Bronze / Frosted Glass
Accessories:
Additional Stem Lengths
25-2078 (6"), **25-2079** (12")





Ballerina Four Light 30" Vanity

*(4) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 30", Height 7⁵/₈", Extension 8¹/₂"
60-3353 Mahogany Bronze / Frosted Glass



Ballerina Three Light 24" Vanity

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24", Height 7⁵/₈", Extension 8¹/₂"
60-3352 Mahogany Bronze / Frosted Glass



Ballerina Five Light 36" Vanity

*(5) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 36", Height 7⁵/₈", Extension 8¹/₂"
60-3354 Mahogany Bronze / Frosted Glass



Ballerina Two Light 18" Vanity

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 18", Height 7⁵/₈", Extension 8¹/₂"
60-3351 Mahogany Bronze / Frosted Glass



Ballerina Seven Light 48" Vanity

*(7) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 48", Height 7⁵/₈", Extension 8¹/₂"
60-3345 Mahogany Bronze / Frosted Glass

Mahogany Bronze with
Frosted White Glass Shades

INTERIOR HOME ES PACKAGE



Empire Two Light Vanity

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-3356 Mahogany Bronze / Frosted Glass



Empire Three Light Vanity

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-3357 Mahogany Bronze / Frosted Glass



Empire One Light Vanity

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-3355 Mahogany Bronze / Frosted Glass



Empire Four Light Vanity

*(4) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-3358 Mahogany Bronze / Frosted Glass



All Energy Saving
Fixtures Include
GU24 Base CFLs



24" Four Light Vanity Strip

†(4) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 24", Height 4 3/4",
Extension 6 1/4" (with lamp)

60-3347 Mahogany Bronze



36" Six Light Vanity Strip

†(6) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 36", Height 4 3/4",
Extension 6 1/4" (with lamp)

60-3348 Mahogany Bronze



18" Three Light Vanity Strip

†(3) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 18", Height 4 3/4",
Extension 6 1/4" (with lamp)

60-3346 Mahogany Bronze



48" Eight Light Vanity Strip

†(8) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 48", Height 4 3/4",
Extension 6 1/4" (with lamp)

60-3349 Mahogany Bronze

Vanity fixtures CUL listed for damp location and glass up or down installation.



All Energy Saving
Fixtures Include
GU24 Base CFLs

Brushed Nickel with Alabaster Glass Shades

Brushed Nickel is accented by Alabaster glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME ES PACKAGE



Two Tier - Nine Light Empire Chandelier

*(9) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-3196 Brushed Nickel / Alabaster Glass

Accessories:

25-1069 3' Section of matching chain





Five Light Ballerina Chandelier

* (5) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 24", Height 18", Chain 48", Wire 12'
60-3180 Brushed Nickel / Alabaster Glass
 Accessories:
25-1069 3' Section of matching chain



Five Light Gotham Chandelier

* (5) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'
60-3182 Brushed Nickel / Alabaster Glass
 Accessories:
25-1069 3' Section of matching chain



Three Light Ballerina Chandelier

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 20", Height 17", Chain 48", Wire 12'
60-3181 Brushed Nickel / Alabaster Glass
 Accessories:
25-1069 3' Section of matching chain



Three Light Gotham Chandelier

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'
60-3183 Brushed Nickel / Alabaster Glass
 Accessories:
25-1069 3' Section of matching chain



Six Light Empire Chandelier

* (6) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 26", Height 14", Chain 48", Wire 12'
60-3195 Brushed Nickel / Alabaster Glass
 Accessories:
25-1069 3' Section of matching chain


Brushed Nickel with
Alabaster Glass Shades

INTERIOR HOME ES PACKAGE



20" Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-3188 Brushed Nickel / Alabaster Glass
Accessories:
25-1069 3' Section of matching chain



15" Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-3187 Brushed Nickel / Alabaster Glass
Accessories:
25-1069 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-3186 Brushed Nickel / Alabaster Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-3185 Brushed Nickel / Alabaster Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-3184 Brushed Nickel / Alabaster Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



All Energy Saving
Fixtures Include
GU24 Base CFLs



11" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 11 3/8", Height 4 7/8"

60-2621 Brushed Nickel / Alabaster Glass

CUL damp location



12" Twist and Lock

*(1) 18WT2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 11 1/2", Height 4 1/2"

60-3201 Brushed Nickel / Alabaster Glass

CUL damp location



13" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 13 1/4", Height 5 3/8"

60-2622 Brushed Nickel / Alabaster Glass

CUL damp location



14" Twist and Lock

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 14", Height 5 1/2"

60-3202 Brushed Nickel / Alabaster Glass

CUL damp location



15" Flush Dome

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 15 1/4", Height 6"

60-2623 Brushed Nickel / Alabaster Glass

CUL damp location



17" Twist and Lock

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 17", Height 6"

60-3203 Brushed Nickel / Alabaster Glass

CUL damp location

Brushed Nickel with
Alabaster Glass Shades

INTERIOR HOME ES PACKAGE



Hanging Dome

(1) 15W CFL Globe / GU24 base / 2700K Included
Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'
60-3198 Brushed Nickel / Alabaster Glass
Accessories:
25-1069 3' Section of matching chain



Pendant Bell

*(1) 18W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'
60-3199 Brushed Nickel / Alabaster Glass
Accessories:
25-2081 3' Section of matching chain



6" Flush Ball

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 7 1/4"
60-3189 Brushed Nickel / Alabaster Glass
CUL damp location



Empire Mini Pendant

with hang-straight canopy
*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7", Height 51" Adjustable, Wire 12'
60-3197 Brushed Nickel / Alabaster Glass
Accessories:
Additional Stem Lengths
25-2047 (6"), **25-2021** (12")





Ballerina Four Light 30" Vanity

* (4) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 30", Height 7 5/8", Extension 8 1/2"
60-3211 Brushed Nickel / Alabaster Glass



Ballerina Three Light 24" Vanity

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24", Height 7 5/8", Extension 8 1/2"
60-3209 Brushed Nickel / Alabaster Glass



Ballerina Five Light 36" Vanity

* (5) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 36", Height 7 5/8", Extension 8 1/2"
60-3212 Brushed Nickel / Alabaster Glass



Ballerina Two Light 18" Vanity

* (2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 18", Height 7 5/8", Extension 8 1/2"
60-3208 Brushed Nickel / Alabaster Glass



Ballerina Seven Light 48" Vanity

* (7) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 48", Height 7 5/8", Extension 8 1/2"
60-3213 Brushed Nickel / Alabaster Glass

Brushed Nickel with
Alabaster Glass Shades

INTERIOR HOME ES PACKAGE



Empire Two Light Vanity

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-3205 Brushed Nickel / Alabaster Glass



Empire Three Light Vanity

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-3206 Brushed Nickel / Alabaster Glass



Empire One Light Vanity

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-3204 Brushed Nickel / Alabaster Glass



Empire Four Light Vanity

*(4) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-3207 Brushed Nickel / Alabaster Glass



All Energy Saving
Fixtures Include
GU24 Base CFLs



24" Four Light Vanity Strip

†(4) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 24", Height 4¾",
Extension 6¼" (with lamp)

60-3302 Brushed Nickel



36" Six Light Vanity Strip

†(6) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 36", Height 4¾",
Extension 6¼" (with lamp)

60-3303 Brushed Nickel



18" Three Light Vanity Strip

†(3) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 18", Height 4¾",
Extension 6¼" (with lamp)

60-3301 Brushed Nickel



48" Eight Light Vanity Strip

†(8) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 48", Height 4¾",
Extension 6¼" (with lamp)

60-3304 Brushed Nickel

interior home es package

Vanity fixtures CUL listed for damp location and glass up or down installation.



All Energy Saving
Fixtures Include
GU24 Base CFLs

Brushed Nickel with
Frosted White Glass Shades

Brushed Nickel is accented by Frosted White glass in this complete product grouping which offers a fixture for every application.

INTERIOR HOME ES PACKAGE



Two Tier - Nine Light Empire Chandelier

*(9) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 32", Height 18", Chain 72", Wire 12'

60-3306 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain





Five Light Ballerina Chandelier

*(5) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24", Height 18", Chain 48", Wire 12'

60-3290 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain



Five Light Gotham Chandelier

*(5) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 24 1/2", Height 17 1/2", Chain 48", Wire 12'

60-3292 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain



Three Light Ballerina Chandelier

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20", Height 17", Chain 48", Wire 12'

60-3291 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain



Three Light Gotham Chandelier

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 22 1/2", Height 17 1/2", Chain 48", Wire 12'

60-3293 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain



Six Light Empire Chandelier

*(6) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 26", Height 14", Chain 48", Wire 12'

60-3305 Brushed Nickel / Frosted Glass

Accessories:

25-1069 3' Section of matching chain

Brushed Nickel with
Frosted White Glass Shades

INTERIOR HOME ES PACKAGE



20" Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20", Height 27³/₄", Chain 48", Wire 12'
60-3298 Brushed Nickel / Frosted Glass
Accessories:
25-1069 3' Section of matching chain



15" Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 23", Chain 48", Wire 12'
60-3297 Brushed Nickel / Frosted Glass
Accessories:
25-1069 3' Section of matching chain



15" Semi-Flush Convertible to Pendant

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15¹/₄", Height 15¹/₂", Wire 12'
60-3296 Brushed Nickel / Frosted Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



13" Semi-Flush Convertible to Pendant

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13¹/₄", Height 14", Wire 12'
60-3295 Brushed Nickel / Frosted Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain



11" Semi-Flush Convertible to Pendant

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11³/₈", Height 12", Wire 12'
60-3294 Brushed Nickel / Frosted Glass
Accessories:
25-1403 Pendant conversion kit
25-1069 3' Section of matching chain





11" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11 3/8", Height 4 7/8"
60-3311 Brushed Nickel / Frosted Glass
CUL damp location



12" Twist and Lock

*(1) 18WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11 1/2", Height 4 1/2"
60-3314 Brushed Nickel / Frosted Glass
CUL damp location



13" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13 1/4", Height 5 3/8"
60-3312 Brushed Nickel / Frosted Glass
CUL damp location



14" Twist and Lock

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 14", Height 5 1/2"
60-3315 Brushed Nickel / Frosted Glass
CUL damp location



15" Flush Dome

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15 1/4", Height 6"
60-3313 Brushed Nickel / Frosted Glass
CUL damp location



17" Twist and Lock

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 17", Height 6"
60-3316 Brushed Nickel / Frosted Glass
CUL damp location

Brushed Nickel with
Frosted White Glass Shades

INTERIOR HOME ES PACKAGE



Hanging Dome

(1) 15W CFL Globel / GU24 base / 2700K Included
Dimensions: Width 16", Height 11 1/2", Chain 48", Wire 12'
60-3308 Brushed Nickel / Frosted Glass
Accessories:
25-1069 3' Section of matching chain



Pendant Bell

*(3) 18W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 3/4", Height 20 1/2", Chain 48", Wire 12'
60-3309 Brushed Nickel / Frosted Glass
Accessories:
25-1069 3' Section of matching chain



6" Flush Ball

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 7 1/4"
60-3299 Brushed Nickel / Frosted Glass
CUL damp location



Empire Mini Pendant

with hang-straight canopy
*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7", Height 51" Adjustable, Wire 12'
60-3307 Brushed Nickel / Frosted Glass
Accessories:
Additional Stem Lengths
25-2047 (6"), **25-2021** (12")





Ballerina Four Light 30" Vanity

* (4) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 30", Height 7 5/8", Extension 8 1/2"
60-3324 Brushed Nickel / Frosted Glass



Ballerina Three Light 24" Vanity

* (3) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 24", Height 7 5/8", Extension 8 1/2"
60-3323 Brushed Nickel / Frosted Glass



Ballerina Five Light 36" Vanity

* (5) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 36", Height 7 5/8", Extension 8 1/2"
60-3325 Brushed Nickel / Frosted Glass



Ballerina Two Light 18" Vanity

* (2) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 18", Height 7 5/8", Extension 8 1/2"
60-3322 Brushed Nickel / Frosted Glass



Ballerina Seven Light 48" Vanity

* (7) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 48", Height 7 5/8", Extension 8 1/2"
60-3327 Brushed Nickel / Frosted Glass

interior home es package

Brushed Nickel with
Frosted White Glass Shades

INTERIOR HOME ES PACKAGE



Empire Two Light Vanity

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 14⁷/₈", Height 6¹/₈", Extension 8"
60-3318 Brushed Nickel / Frosted Glass



Empire Three Light Vanity

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 20¹/₂", Height 6¹/₈", Extension 8"
60-3319 Brushed Nickel / Frosted Glass



Empire One Light Vanity

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6¹/₄", Height 6¹/₈", Extension 9"
60-3317 Brushed Nickel / Frosted Glass



Empire Four Light Vanity

*(4) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 28³/₄", Height 6¹/₈", Extension 8"
60-3321 Brushed Nickel / Frosted Glass



All Energy Saving
Fixtures Include
GU24 Base CFLs



24" Four Light Vanity Strip

†(4) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 24", Height 4¾",
Extension 6¼" (with lamp)

60-3302 Brushed Nickel



36" Six Light Vanity Strip

†(6) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 36", Height 4¾",
Extension 6¼" (with lamp)

60-3303 Brushed Nickel



18" Three Light Vanity Strip

†(3) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 18", Height 4¾",
Extension 6¼" (with lamp)

60-3301 Brushed Nickel



48" Eight Light Vanity Strip

†(8) 15W CFL Globe / GU24 base / 2700K Included

Dimensions: Width 48", Height 4¾",
Extension 6¼" (with lamp)

60-3304 Brushed Nickel

Vanity fixtures CUL listed for damp location and glass up or down installation.



All Energy Saving
Fixtures Include
GU24 Base CFLs

ES WALL FIXTURES

CUL listed for damp location / ADA Compliant



All Energy Saving
Fixtures Include
GU24 Base CFLs



Wall Sconce

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 12 1/2", Height 7 3/8", Extension 4"

60-2951 Brushed Nickel / Opal Glass



Wall Sconce

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 12", Height 12 1/2", Extension 3"

60-940 Brushed Nickel / Frosted Glass



Wall Sconce

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 9", Height 10", Extension 4"

60-946 Brushed Nickel / Frosted Glass



Wall Sconce

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 9", Height 10", Extension 4"

60-944 Brushed Nickel / Frosted Glass



Wall Sconce

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 9", Height 10", Extension 4"

60-948 Brushed Nickel / Frosted Glass

ES WALL FIXTURES

CUL listed for damp location / ADA Compliant



Wall Sconce

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 7 1/4", Extension 3 1/2"
60-936 Brushed Nickel / Frosted Glass



Crispo Wall Sconce

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9", Height 10 1/2", Extension 4"
60-923 White / White Acrylic



Wall Sconce

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 7", Extension 4"
60-938 Brushed Nickel / Frosted Glass



Rustica Wall Sconce

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9", Height 10 1/2", Extension 4"
60-931 Old Bronze / White Acrylic



Glamour Wall Sconce

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9", Height 10 1/2", Extension 4"
60-907 Brushed Nickel / White Acrylic
60-915 Old Bronze / White Acrylic


es wall fixtures

ES WALL FIXTURES

CUL listed for damp location / ADA Compliant



All Energy Saving Fixtures
Include GU24 Base CFLs
(except linear fluorescent)



25" Glamour Vanity

*(2) F17T8 max.

Dimensions: Width 25", Height 5 1/2", Extension 3"

60-906R Brushed Nickel / White Acrylic

49" Glamour Vanity

*(2) F32T8 max.

Dimensions: Width 49", Height 5 1/2", Extension 3"

60-904R Brushed Nickel / White Acrylic



25" Glamour Vanity

*(2) F17T8 max.

Dimensions: Width 25", Height 5 1/2", Extension 3"


60-914R Old Bronze / White Acrylic

49" Glamour Vanity

*(2) F32T8 max.

Dimensions: Width 49", Height 5 1/2", Extension 3"

60-912R Old Bronze / White Acrylic



25" Crispo Vanity

*(2) F17T8 max.

Dimensions: Width 25", Height 5 1/2", Extension 3"

60-922R White / White Acrylic

49" Crispo Vanity

*(2) F32T8 max.

Dimensions: Width 49", Height 5 1/2", Extension 3"

60-920R White / White Acrylic



25" Rustica Vanity

*(2) F17T8 max.

Dimensions: Width 25", Height 5 1/2", Extension 3"

60-930R Old Bronze / White Acrylic

49" Rustica Vanity

*(2) F32T8 max.

Dimensions: Width 49", Height 5 1/2", Extension 3"

60-928R Old Bronze / White Acrylic

ES CEILING FIXTURES

CUL listed for damp location



Small Crispo Round

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 12", Height 4"

60-916 White / White Acrylic

Medium Crispo Round

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 14", Height 5 1/2"


60-917 White / White Acrylic

Large Crispo Round

*(3) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 18", Height 5"

60-918 White / White Acrylic



25" Crispo Linear

*(3) F17T8 max.

Dimensions: Length 25", Width 4 1/2", Height 12"

60-921R White / White Acrylic

50" Crispo Linear

*(3) F32T8 max.

Dimensions: Length 50", Width 4 1/2", Height 12"

60-919R White / White Acrylic



Small Rustica Round

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 14", Height 5"

60-924 Old Bronze / White Acrylic

Medium Rustica Round

*(3) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 17", Height 5 1/2"

60-925 Old Bronze / White Acrylic

Large Rustica Round

*(3) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 27", Height 6"

60-926 Old Bronze / White Acrylic



25" Rustica Linear

*(3) F17T8 max.

Dimensions: Length 25", Width 4 1/2", Height 12"

60-929R Old Bronze / White Acrylic

50" Rustica Linear

*(3) F32T8 max.

Dimensions: Length 50", Width 4 1/2", Height 12"

60-927R Old Bronze / White Acrylic

es wall / ceiling fixtures

ES CEILING FIXTURES

CUL listed for damp location



All Energy Saving Fixtures
Include GU24 Base CFLs
(except linear fluorescent)



Small Glamour Round

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 13", Height 3 3/4"

60-900 Brushed Nickel / White Acrylic

Medium Glamour Round

*(3) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 17", Height 3 3/4"

60-901 Brushed Nickel / White Acrylic

Large Glamour Round

*(3) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 24", Height 3 3/4"

60-902 Brushed Nickel / White Acrylic



Small Glamour Round

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 13", Height 3 3/4"

60-908 Old Bronze / White Acrylic

Medium Glamour Round

*(3) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 17", Height 3 3/4"

60-909 Old Bronze / White Acrylic

Large Glamour Round

*(3) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 24", Height 3 3/4"

60-910 Old Bronze / White Acrylic



25" Glamour Linear

*(3) F17T8 max.

Dimensions: Length 25", Width 4 1/2", Height 12"

60-905R Brushed Nickel / White Acrylic

50" Glamour Linear

*(2) F32T8 max.

Dimensions: Length 50", Width 4 1/2", Height 12"

60-903R Brushed Nickel / White Acrylic



25" Glamour Linear

*(3) F17T8 max.

Dimensions: Length 25", Width 4 1/2", Height 12"

60-913R Old Bronze / White Acrylic

50" Glamour Linear

*(2) F32T8 max.

Dimensions: Length 50", Width 4 1/2", Height 12"

60-911R Old Bronze / White Acrylic

ES CEILING FIXTURES

CUL listed for damp location



Glamour Oval

(2) PLL36W / 2G11 base max.

Dimensions: Length 32½", Width 18", Height 4"

60-998 Brushed Nickel / White Acrylic

Glamour Oval

(2) PLL36W / 2G11 base max.

Dimensions: Length 32½", Width 18", Height 4"

60-999 Old Bronze / White Acrylic



Small Button Round

* (1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 11", Height 3⅞"

60-2941 Brushed Nickel / White Glass

Medium Button Round

* (2) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 13⅜", Height 4"

60-2944 Brushed Nickel / White Glass

Large Button Round

* (4) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 17", Height 5"

60-2947 Brushed Nickel / White Glass



Small Button Round

* (1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 11", Height 3⅞"

60-2942 Aged Bronze / White Glass

Medium Button Round

* (2) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 13⅜", Height 4"

60-2945 Aged Bronze / White Glass

Large Button Round

* (4) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 17", Height 5"

60-2948 Aged Bronze / White Glass



Small Button Round

* (1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 11", Height 3⅞"

60-2943 Textured Black / White Glass

Medium Button Round

* (2) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 13⅜", Height 4"

60-2946 Textured Black / White Glass

Large Button Round

* (4) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 17", Height 5"

60-2949 Textured Black / White Glass

es ceiling fixtures

ES CEILING

CUL listed for damp location



All Energy Saving
Fixtures Include
GU24 Base CFLs



11" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11", Height 5 1/4"

60-443 Textured White / Frosted Melon Glass

13" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13", Height 5 1/2"

60-444 Textured White / Frosted Melon Glass

15" Flush Dome

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 6"

60-445 Textured White / Frosted Melon Glass



11" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11", Height 5 1/4"

60-440 Polished Brass / Frosted Melon Glass

13" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13", Height 5 1/2"

60-441 Polished Brass / Frosted Melon Glass

15" Flush Dome

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 6"

60-442 Polished Brass / Frosted Melon Glass



11" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11", Height 5 1/4"

60-446 Brushed Nickel / Frosted Melon Glass

13" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13", Height 5 1/2"

60-447 Brushed Nickel / Frosted Melon Glass

15" Flush Dome

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 6"

60-448 Brushed Nickel / Frosted Melon Glass



11" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11", Height 5 1/4"

60-449 Old Bronze / Frosted Melon Glass

13" Flush Dome

*(2) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13", Height 5 1/2"

60-450 Old Bronze / Frosted Melon Glass

15" Flush Dome

*(3) 13WT2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15", Height 6"

60-451 Old Bronze / Frosted Melon Glass

ES CEILING

CUL listed for damp location,(except R30 Bullet Swivels)



11" Flush Dome

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11 3/8", Height 4 7/8"

60-2628 Textured White / Alabaster Glass

13" Flush Dome

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13 1/4", Height 5 3/8"

60-2629 Textured White / Alabaster Glass

15" Flush Dome

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15 1/4", Height 6"

60-2631 Textured White / Alabaster Glass



11" Flush Dome

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 11 3/8", Height 4 7/8"

60-2624 Old Bronze / Alabaster Glass

13" Flush Dome

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 13 1/4", Height 5 3/8"

60-2625 Old Bronze / Alabaster Glass

15" Flush Dome

*(3) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 15 1/4", Height 6"

60-2627 Old Bronze / Alabaster Glass



Small Mushroom

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7 1/2", Height 5"

60-2651 Mahogany Bronze / Frosted Glass

Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 6"

60-2653 Mahogany Bronze / Frosted Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-2655 Mahogany Bronze / Frosted Glass



Small Mushroom

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7 1/2", Height 5"

60-2652 Mahogany Bronze / Champagne Linen Glass

Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 6"

60-2654 Mahogany Bronze / Champagne Linen Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-2656 Mahogany Bronze / Champagne Linen Glass

es ceiling fixtures

ES CEILING FIXTURES

CUL listed for damp location



All Energy Saving
Fixtures Include
GU24 Base CFLs



Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 5"

60-401 Polished Brass / White Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-402 Polished Brass / White Glass



Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 5"

60-403 White / White Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-404 White / White Glass



Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 5"

60-405 Brushed Nickel / White Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-406 Brushed Nickel / White Glass



Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 5"

60-407 Old Bronze / White Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-408 Old Bronze / White Glass

ES CEILING FIXTURES

CUL listed for damp location



Small Mushroom

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7 1/2", Height 5"

60-2633 Brushed Nickel / Alabaster Glass

Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 6"

60-2635 Brushed Nickel / Alabaster Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-414 Brushed Nickel / Alabaster Glass



Small Mushroom

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7 1/2", Height 5"

60-2636 Textured White / Alabaster Glass

Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 6"

60-2637 Textured White / Alabaster Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-412 Textured White / Alabaster Glass



Small Mushroom

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7 1/2", Height 5"

60-2632 Old Bronze / Alabaster Glass

Medium Mushroom

*(2) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 9 1/2", Height 6"

60-2634 Old Bronze / Alabaster Glass

Large Mushroom

*(2) 18W T3 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 12", Height 6 1/2"

60-416 Old Bronze / Alabaster Glass



8" Flush Ball

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 8", Height 9 1/2"

60-430 White / White Glass

60-433 Old Bronze / White Glass

60-431 Polished Brass / White Glass

60-432 Brushed Nickel / White Glass

6" Flush Ball

*(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 6", Height 7 1/4"

60-436 White / White Glass

es ceiling fixtures

Well-lit residences begin outside.



Outdoor lighting is, well, essential. Nothing makes a home or complex safer or more welcoming after dark than a well-planned outdoor lighting design, and no lighting manufacturer offers more ways to help than Nuvo.

Our Basics outdoor collections include hanging lanterns, wall-, flush- and pole-mounted fixtures, as well as floods, spots, pathway and landscape lighting -- all coordinated in styles that range from classic to contemporary and even industrial. But there's more ...

Nuvo outdoor fixtures have the detail, the finishes and a variety of shapes and styles to make every structure a destination. As one approaches a private home, apartment or condo complex, or office building, these details are making a subconscious yet instant impression on visitors.



detail

From the soft oval of the Clear Beveled glass panels to the detailed finials and hood, this is a timeless design that evokes an elegant era.



CENTRAL PARK



Large Wall Lantern / Arm Up

(3) 60W Type B max. / Candelabra base
Dimensions: Width 7³/₈", Height 22³/₄", Extension 11¹/₂",
Top to Outlet 15"

- 60-888 White / Clear Beveled Panels
- 60-889 Old Bronze / Clear Beveled Panels
- 60-890 Textured Black / Clear Beveled Panels

Large Wall Lantern / Arm Down

(3) 60W Type B max. / Candelabra base
Dimensions: Width 7³/₈", Height 22³/₄", Extension 11¹/₂",
Top to Outlet 9"

- 60-891 White / Clear Beveled Panels
- 60-892 Old Bronze / Clear Beveled Panels
- 60-893 Textured Black / Clear Beveled Panels



Small Wall Lantern / Arm Up

(1) 100W A19 max. / Med. base

Dimensions: Width 6", Height 20", Extension 9³/₄",
Top to Outlet 13"

60-885 White / Clear Beveled Panels

60-886 Old Bronze / Clear Beveled Panels

60-887 Textured Black / Clear Beveled Panels



Hanging Lantern

(3) 60W Type B max. / Candelabra base

Dimensions: Width 7³/₈", Height 20", Chain 48", Wire 12'

60-894 White / Clear Beveled Panels

60-895 Old Bronze / Clear Beveled Panels

60-896 Textured Black / Clear Beveled Panels

Accessories:

25-1166 3' Section of White chain

25-1067 3' Section of Old Bronze chain

25-1071 3' Section of Textured Black chain



Post Lantern

(3) 60W Type B max. / Candelabra base

Dimensions: Width 7³/₈", Height 21"

60-897 White / Clear Beveled Panels

60-898 Old Bronze / Clear Beveled Panels

60-899 Textured Black / Clear Beveled Panels

Accessories:

25-1205 White pier mount base

25-1203 Old Bronze pier mount base

25-1200 Textured Black pier mount base



Cornerstone's long, tapered cage is elegant in its simplicity. Clear Seeded glass and gentle details enable this collection to make a statement on homes from classic to contemporary.

CORNERSTONE



Wall Lantern / Arm Up

Long & Short Tail Provided
(shown with long tail)

(1) 60W A19 max. / Medium base

Dimensions: Width 7", Height 12", Extension 9 1/4",
Top to Outlet 11"

60-985 White / Clear Seeded Glass

60-986 Old Bronze / Clear Seeded Glass

60-987 Textured Black / Clear Seeded Glass

Wall Lantern / Arm Up

(shown with short tail)



Wall Lantern / Arm Down

(1) 60W A19 max. / Medium base

Dimensions: Width 7", Height 13", Extension 9 1/4",
Top to Outlet 4"

60-988 White / Clear Seeded Glass

60-989 Old Bronze / Clear Seeded Glass

60-990 Textured Black / Clear Seeded Glass



Hanging Lantern

(1) 60W A19 max. / Medium base

Dimensions: Width 7", Height 12 5/8", Chain 48", Wire 12'

60-991 White / Clear Seeded Glass

60-992 Old Bronze / Clear Seeded Glass

60-993 Textured Black / Clear Seeded Glass

Accessories:

25-1166 3' Section of White chain

25-1067 3' Section of Old Bronze chain

25-1071 3' Section of Textured Black chain



Post Lantern

(1) 60W A19 max. / Medium base

Dimensions: Width 7", Height 14 1/4"

60-994 White / Clear Seeded Glass

60-995 Old Bronze / Clear Seeded Glass

60-996 Textured Black / Clear Seeded Glass

Accessories:

25-1205 White pier mount base

25-1203 Old Bronze pier mount base

25-1200 Textured Black pier mount base

cornerstone

Open, clean design, Clear glass and tall hood give the Briton collection a character that's classically simple and comfortable with many architectural styles.

BRITON



Wall Lantern / Arm Up

Long & Short Tail Provided
(shown with long tail)

(1) 60W A19 max. / Medium base

Dimensions: Width 6", Height 18", Extension 6 1/8",
Top to Outlet 12"

60-540 White / Clear Glass

60-541 Old Bronze / Clear Glass

60-542 Textured Black / Clear Glass

Wall Lantern / Arm Up

(shown with short tail)



Hanging Lantern

- (1) 60W A19 max. / Medium base
- Dimensions: Width 6", Height 9 1/2", Chain 48", Wire 12'
- 60-487** White / Clear Glass
- 60-488** Old Bronze / Clear Glass
- 60-489** Textured Black / Clear Glass
- Accessories:
- 25-1166** 3' Section of White chain
- 25-1067** 3' Section of Old Bronze chain
- 25-1071** 3' Section of Textured Black chain

Post Lantern

- (1) 60W A19 max. / Medium base
- Dimensions: Width 6", Height 14"
- 60-546** White / Clear Glass
- 60-547** Old Bronze / Clear Glass
- 60-548** Textured Black / Clear Glass
- Accessories:
- 25-1205** White pier mount base
- 25-1203** Old Bronze pier mount base
- 25-1200** Textured Black pier mount base

All fixtures CUL wet location listed except hanging lanterns, (damp location listed).

These timeless designs, offered in three finishes, are the quickest way to improve curb appeal for a wide variety of home styles.

SMALL WALL LANTERNS



Onion Lantern

(1) 60W A19 max. / Medium base

Dimensions: Width 6", Height 10⁵/₈", Extension 8",
Top to Outlet 6"

60-630 White / Clear Seed Glass

60-631 Old Bronze / Clear Seed Glass

60-632 Textured Black / Clear Seed Glass

Piper Lantern

(1) 60W A19 max. / Medium base

Dimensions: Width 5", Height 10⁵/₈", Extension 7",
Top to Outlet 6"

60-633 White / Clear Seed Glass

60-634 Old Bronze / Clear Seed Glass

60-635 Textured Black / Clear Seed Glass





small wall lanterns



Cube Lantern

- (1) 60W A19 max. / Medium base
- Dimensions: Width 4³/₈", Height 8⁵/₈", Extension 6¹/₈", Top to Outlet 3"
- 60-636 White / Clear Beveled Glass
- 60-637 Old Bronze / Clear Beveled Glass
- 60-638 Textured Black / Clear Beveled Glass



Hood Lantern

- (1) 60W A19 max. / Medium base
- Dimensions: Width 6", Height 8⁷/₈", Extension 6⁷/₈", Top to Outlet 5"
- 60-639 White / Satin Frosted Glass
- 60-640 Old Bronze / Satin Frosted Glass
- 60-641 Textured Black / Satin Frosted Glass

These tough fixtures withstand weather extremes in stylish fashion. Many styles to choose from, all with thick glass and reinforced cages that protect lamps from exposure and perfect for every nautical-themed design.



DIE CAST BULKHEADS



Round Hood

(1) 60W A19 max. / Medium base
 *(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 10", Extension 5"
60-520 Semi Gloss White
60-564* Semi Gloss White
60-521 Architectural Bronze
60-565* Architectural Bronze



Oval Cage

(1) 60W A19 max. / Medium base
 *(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 6 1/8", Height 10", Extension 5 1/2"
60-524 Semi Gloss White
60-568* Semi Gloss White
60-525 Architectural Bronze
60-569* Architectural Bronze



Oval Hood

(1) 60W A19 max. / Medium base
 *(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 10", Height 6 1/8", Extension 5 1/2"
60-522 Semi Gloss White
60-566* Semi Gloss White
60-523 Architectural Bronze
60-567* Architectural Bronze



All Energy Saving
 Fixtures Include
 GU24 Base CFLs



Rectangle

(1) 60W A19 max. / Medium base
 *(1) 18W T3 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 6 1/2", Height 10", Extension 4 7/8"
60-530 Semi Gloss White
60-574* Semi Gloss White
60-531 Architectural Bronze
60-575* Architectural Bronze



Rectangle Cage

(1) 60W A19 max. / Medium base
 *(1) 18W T3 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 6 1/2", Height 10", Extension 4 7/8"
60-532 Semi Gloss White
60-576* Semi Gloss White
60-533 Architectural Bronze
60-577* Architectural Bronze



Large Oval

(1) 60W A19 max. / Medium base
 *(1) 18W T3 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 9", Height 11", Extension 4 3/8"
60-526 Semi Gloss White
60-570* Semi Gloss White
60-527 Architectural Bronze
60-571* Architectural Bronze



Large Oval Cage

(1) 60W A19 max. / Medium base
 *(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 8 1/2", Height 12 1/2", Extension 5"
60-528 Semi Gloss White
60-572* Semi Gloss White
60-529 Architectural Bronze
60-573* Architectural Bronze



Oblong Round

(1) 60W A19 max. / Medium base
 *(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 10 1/2", Height 9 1/8", Extension 4 1/2"
60-516 Semi Gloss White
60-560* Semi Gloss White
60-517 Architectural Bronze
60-561* Architectural Bronze



Round Cage

(1) 60W A19 max. / Medium base
 *(1) 18W T3 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 10", Extension 5"
60-518 Semi Gloss White
60-562* Semi Gloss White
60-519 Architectural Bronze
60-563* Architectural Bronze



WALL & FLUSH



Cage Lantern

Die Cast / Linen Acrylic Lens

(1) 60W A19 max. / Medium base

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 7³/₄", Height 9³/₄", Extension 4¹/₄"

60-537 White

60-581* White

60-538 Old Bronze

60-582* Old Bronze

60-539 Textured Black

60-583* Textured Black

Ceiling "Spider" Cage

Die Cast / Glass Lens

(1) 60W A19 max. / Medium base

*(1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 11³/₈", Height 5"

60-534 White

60-578* White

60-535 Old Bronze

60-579* Old Bronze

60-536 Textured Black

60-580* Textured Black



All Energy Saving
Fixtures Include
GU24 Base CFLs



Round Cage

Polysynthetic Body and Lens

(1) 60W A19 max. / Medium base

†(2) 9W Twin/G23 base max. Included


Dimensions: Height 10", Extension 4"

77-861 White

77-892† White

77-859 Black

77-893† Black



Oval Cage

Polysynthetic Body and Lens

(1) 60W A19 max. / Medium base

†(1) 9W Twin/G23 base max. Included

Dimensions: Width 10", Height 5", Extension 4"

77-858 White

77-894† White

77-857 Black

77-895† Black

Style and function combine to create fixtures that are so distinctive and versatile, they can set the tone for an entire property! Rugged and interesting, available in three popular finishes.



INDUSTRIAL STYLE SURFACE MOUNT



Large Die-Cast Ceiling Mount

(1) 200W A19 max. / Med. base

Dimensions: Height 11", Width 5 1/2"

76-618 White / Frosted Glass

76-626 Metallic Silver / Frosted Glass

76-627 Old Bronze / Frosted Glass

Small Die-Cast Ceiling Mount

(1) 100W A19 max. / Med. base

Dimensions: Height 9 3/8", Width 4 1/4"

76-616 White / Frosted Glass

76-624 Metallic Silver / Frosted Glass

76-625 Old Bronze / Frosted Glass



Die-Cast Junction Boxes
(can be added to wall fixtures)

- 76-650 White
- 76-651 Metallic Silver
- 76-652 Old Bronze



Large Die-Cast Wall Mount

- (1) 300W A19 max. / Med. base
- Dimensions: Height 11", Width 5 1/2", Extension 6 3/8"
- 76-617 White / Frosted Glass
- 76-622 Metallic Silver / Frosted Glass
- 76-623 Old Bronze / Frosted Glass




Small Die-Cast Wall Mount

- (1) 150W A19 max. / Med. base
- Dimensions: Height 9 3/8", Width 4 1/4", Extension 5 3/8"
- 76-615 White / Frosted Glass
- 76-620 Metallic Silver / Frosted Glass
- 76-621 Old Bronze / Frosted Glass

industrial style

CARPORT FLUSH MOUNTS



Small Poly Frame

(1) 60W A19 max. / Medium base
Dimensions: Width 8 1/4", Height 4 3/4"

77-835 White / Frosted Glass

77-863 Black / Frosted Glass



Metal Frame

(2) 60W A19 max. / Medium base
Dimensions: Width 9 1/4", Height 5"

60-470 White / Textured Frosted Glass

60-471 Polished Brass / Textured Frosted Glass

60-472 Old Bronze / Textured Frosted Glass

60-473 Black / Textured Frosted Glass

Large Poly Frame

(2) 60W A19 max. / Medium base
Dimensions: Width 10 1/4", Height 5 1/2"

77-879 White / Frosted Glass

77-891 Black / Frosted Glass

UTILITY FIXTURES



Wall Mount–Globe

(1) 100W A19 max. / Medium base
 Dimensions: Width 7¼", Height 6", Extension 7"
77-531 White / White Glass
77-139 Satin Aluminum / White Glass
77-141 Bronzotic / White Glass
77-140 Black / White Glass



Ceiling Mount–Cylinder

(1) 60W A19 max. / Medium base
 Dimensions: Width 8", Height 4¼"
77-533 White / White Glass
77-155 Satin Aluminum / White Glass
77-156 Bronzotic / White Glass
77-154 Black / White Glass



Ceiling Mount–Globe

(1) 60W A19 max. / Medium base
 Dimensions: Width 7¼", Height 6"
77-532 White / White Glass
77-152 Satin Aluminum / White Glass
77-153 Bronzotic / White Glass
77-157 Black / White Glass



Wall Mount–Cylinder

(1) 100W A19 max. / Medium base
 Dimensions: Width 8", Height 4¾", Extension 6"
77-530 White / White Glass
77-136 Satin Aluminum / White Glass
77-138 Bronzotic / White Glass
77-137 Black / White Glass

carport/utility

PORCH WALL FIXTURES



White Glass Globe

(1) 60W A19 max. / Medium base

Dimensions: Width 5 1/2", Height 8 1/2", Extension 6"

76-704 Gloss White / White Glass

76-705 Brushed Nickel / White Glass

77-992 Black / White Glass

76-703 Old Bronze / White Glass



Clear Mason Jar

(1) 60W A19 max. / Medium base

Dimensions: Width 4", Height 8 1/2", Extension 5 1/2"

77-119 Black / Clear Ribbed Glass

77-996 Polished Brass Finish / Clear Ribbed Glass

77-995 Antique Brass Finish / Clear Ribbed Glass



Frosted Mason Jar

(1) 60W A19 max. / Medium base

Dimensions: Width 4", Height 8 1/2", Extension 5 1/2"

76-701 Brushed Nickel / Frosted Ribbed Glass

76-700 Old Bronze / Frosted Ribbed Glass

76-702 Gloss White / Frosted Ribbed Glass



Clear Mason Jar
with Photoelectric Sensor

(1) 60W A19 max. / Medium base

Dimensions: Width 4 1/2", Height 6", Extension 6"

77-862 White / Clear Ribbed Glass

77-856 Black / Clear Ribbed Glass



Lexan Cylinder

*Requires (1) 13W Quad tube GX23-2 Base max.

Dimensions: Width 4", Height 8", Extension 6"

77-727† White / White Lexan Cylinder – Energy Efficient

77-726† Black / White Lexan Cylinder – Energy Efficient



Lexan Cylinder

with Photoelectric Sensor

*Requires (1) 13W Quad tube GX23-2 Base max.

Dimensions: Width 4", Height 8", Extension 6"

77-749† White / White Lexan Cylinder – Energy Efficient

77-748† Black / White Lexan Cylinder – Energy Efficient



Lexan Globe

*Requires (1) 13W Quad tube GX23-2 Base max.

Dimensions: Width 6", Height 8", Extension 7 3/4"

77-729† White / White Lexan Globe – Energy Efficient

77-728† Black / White Lexan Globe – Energy Efficient



Lexan Globe

with Photoelectric Sensor

*Requires (1) 13W Quad tube GX23-2 Base max.

Dimensions: Width 6", Height 8", Extension 7 3/4"

77-751† White / White Lexan Globe – Energy Efficient

77-750† Black / White Lexan Globe – Energy Efficient



The weather is no match for these timeless styles. Poly hoods, cages and wall plates with Clear Acrylic panels stand up to the elements while adding elegance to any home.

POLY LANTERNS



Coach Wall Lantern

(1) 60W A19 max. / Medium base
Dimensions: Width 7³/₄", Height 17", Extension 8"
Top to Outlet 12"
77-897 White / Acrylic Panels
77-896 Black / Acrylic Panels



Mansard Wall Lantern

(1) 60W A19 max. / Medium base
Dimensions: Width 8", Height 17¹/₂", Extension 8",
Top to Outlet 12"
77-853 White / Textured Acrylic Panels
77-852 Black / Textured Acrylic Panels



Coach Post Lantern

(1) 60W A19 max. / Medium base
Dimensions: Width 7³/₄", Height 12¹/₂",
77-899 White / Acrylic Panels
77-898 Black / Acrylic Panels

Add safety and clarity to larger outdoor spaces, including driveways, yards and parking areas—there are so many uses—with Halogen lighting. Available in Bronze, with or without motion detectors.

EXTERIOR HALOGEN FLOODLIGHTS



Mini Halogen Floodlight

(1) 150W Type J 78mm Halogen bulb - Included
 Dimensions: Width 5", Height 3 1/4", Extension 8"
 76-511 Bronze



Twin Mini Halogen Floodlight

(2) 150W Type J 78mm Halogen bulb - Included
 Dimensions: Width 15", Height 3 1/4", Extension 8"
 76-513 Bronze



Mini Halogen Floodlight
 with Motion Sensor

(1) 150W Type J 78mm Halogen bulb - Included
 Dimensions: Width 5", Height 6", Extension 8"
 76-505 Bronze



Twin Mini Halogen Floodlight
 with Motion Sensor

(2) 150W Type J 78mm Halogen bulb - Included
 Dimensions: Width 15", Height 7", Extension 8"
 76-507 Bronze

lanterns / floodlights

Add safety to the entire property with these handsome exterior fixtures which are available with or without motion sensors.



EXTERIOR FLOODLIGHTS



Cast Aluminum One Light PAR38 Floodlights

(1) 150W PAR38 max. / Medium base
Dimensions: Width 4 1/2", Extension 8"

- 77-487 White
- 77-702 Gray
- 77-494 Bronze
- 77-700 Black

Add On Motion Sensors

Fits 1/2" Threaded Knockouts

- 76-500 White
- 76-501 Bronze



Cast Aluminum Two Light PAR38 Floodlights

(2) 150W PAR38 max. / Medium base
Dimensions: Width 15", Extension 8"

- 77-488 White
- 77-703 Gray
- 77-495 Bronze
- 77-701 Black



**2 Light "Quick Mount"
Adjustable PAR Holders**

(2) 150W PAR38 max.

Dimensions: Width 8¾", Extension 3¼"

76-684 White

76-685 Bronze



**1 Light "Quick Mount"
Adjustable PAR Holders**

(1) 150W PAR38 max.

Dimensions: Width 5", Extension 3¼"

76-682 White

76-683 Bronze



2 Light PAR Floodlight Holders

(2) 150W PAR38 max.

Dimensions: Width 10", Extension 5"

76-522 White

76-523 Bronze



1 Light PAR Floodlight Holders

(1) 150W PAR38 max.

Dimensions: Width 4½", Extension 5"

76-520 White

76-521 Bronze



**2 Light PAR Floodlight Holders
with Motion Sensor**

(2) 150W PAR38 max.

Dimensions: Width 10", Extension 9½"

76-502 White

76-503 Bronze



**2 Light PAR38 Floodlights
with Motion Sensor**

(2) 150W PAR38 max.

Dimensions: Width 14", Extension 9½"

76-530 White

76-531 Bronze

Outdoor lighting isn't just a requirement.



It's an opportunity.

Most local building codes set minimum safety standards for the exterior lighting of homes, apartment and condominium complexes. But supplementing mandated lighting with well-placed decorative and landscape fixtures is an inexpensive way to increase the warmth and beauty of any property's outdoor lighting plan, adding real value in the minds of owners and potential buyers. All of Nuvo's outdoor collections feature high-quality lighting systems that let architects, landscape designers and home owners accentuate their work with coordinated fixtures that look as good by day as they do at night.



accentuate

Landscaping comes to life at night with these attractive fixtures. Entire gardens and yards can be illuminated for both beauty and safety with little or no intrusion on the overall landscape design.

LANDSCAPE FLOOD LIGHTS



1 and 2 Light Die Cast Mounting Plates

76-665 1 Light / Dark Bronze

76-666 2 Light / Dark Bronze

76-667 1 Light / Antique Verdi

76-668 2 Light / Antique Verdi



Hardware and gasket included



CFL Landscape Floodlight with Photocell

(1) 18W T3 Mini Spiral / GU24 base / 2700K Included

Dimensions: Diameter 5 1/2", Length 12 1/2"

76-748 Dark Bronze – Energy Efficient

CFL Landscape Floodlight with Photocell

(1) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Diameter 4 1/4", Length 11 1/2"

76-747 Dark Bronze – Energy Efficient





PAR20 Landscape Floodlight

(1) 50W PAR20 max.

Dimensions: Diameter 2 3/4", Length 6 1/4"

76-646 Dark Bronze

76-656 Antique Verdi



PAR16 Landscape Floodlight

(1) 50W PAR16 max.

Dimensions: Diameter 2 1/2", Length 5 1/2"

76-645 Dark Bronze

76-655 Antique Verdi



PAR38 Landscape Floodlight

(1) 150W PAR38 max.

Dimensions: Diameter 5 1/2", Length 12 1/2"

76-648 Dark Bronze

76-658 Antique Verdi



PAR30 Landscape Floodlight

(1) 75W PAR30 (Longneck) max.

Dimensions: Diameter 4 1/4", Length 11 1/2"

76-647 Dark Bronze

76-657 Antique Verdi



Beauty and safety from one fixture!
 Light the way with classic pathway
 lighting systems, available in Old Bronze
 or Green to blend into, yet complement
 virtually any garden path or walkway.



PATHWAY LIGHTING



12" X 1/2" Steel Mounting Post
 Threaded on Both Ends

90-1278 Green Finish

90-1279 Old Bronze Finish



Three Louver Small Hood

(1) 100W A19 max. / Medium base

Dimensions: Height 8 5/8", Diameter 6 1/8"

76-633 Old Bronze

77-324 Green



Two Louver Small Hood

(1) 75W A19 max. / Medium base

Dimensions: Height 7 1/8", Diameter 6 1/8"

76-632 Old Bronze

77-323 Green



3" Diameter PVC Mounting Post

Dimensions: Height 18", Diameter 3"

76-641 Dark Bronze

76-664 Antique Verdi Finish



2" Diameter PVC Mounting Post

Dimensions: Height 18", Diameter 2"

76-638 Green Finish

76-639 Old Bronze Finish

76-640 Dark Bronze Finish

76-644 Antique Verdi Finish



Three Louver Large Hood

(1) 100W A19 max. / Medium base

Dimensions: Height 8⁵/₈", Diameter 9⁵/₈"

76-637 Old Bronze

76-636 Green



Two Louver Large Hood

(1) 75W A19 max. / Medium base

Dimensions: Height 7¹/₈", Diameter 9⁵/₈"

76-635 Old Bronze

76-634 Green

Choose a globe and holder to create a complete fixture. Globe and holders sold separately. Acrylic globes have 1/4 turn twist lock notched holders for easy relamping. Holders fit all standard 3" posts and pier mount bases.

TWIST LOCK GLOBES, HOLDERS & PIER MOUNT BASES



White Acrylic Globe

Item #	Diameter	Fitter
50-784	10"	4"
50-785	12"	5 1/4"
50-786	14"	5 1/4"
50-787	16"	5 1/4"

Smoke Acrylic Globe

Item #	Diameter	Fitter
50-780	10"	4"
50-781	12"	5 1/4"
50-782	14"	5 1/4"
50-783	16"	5 1/4"



5" Round Pier Mount Bases

- 25-1206 Antique Brass
- 25-1207 Polished Brass
- 25-1208 Brushed Nickel



6" Square Pier Mount Bases

- | | |
|---------------------------|-------------------------|
| 25-1200 Textured Black | 25-4026* Burlwood |
| 25-1203 Old Bronze | 25-4908* Rustic Bronze |
| 25-1204 Old Penny Bronze | 25-5605* Stone Black |
| 25-1205 White | 25-5615* Classic Bronze |
| 25-4021* Fruitwood | 25-5635* Aged Silver |
| 25-4023* Satin Iron Ore | 25-5645* Claret Bronze |
| 25-4024* Belgium Bronze | 25-5655* Umber Bronze |
| 25-4025* Dark Plum Bronze | |

*(not shown)



Incandescent Twist Lock Holders

Incandescent Maximum Wattages

- 10" Globes – 60 watt max.
- 12" to 14" – 100 watt max.
- 16" – 150 watt max.

- 77-692 4" Black
- 77-693 4" White
- 77-968 5 1/2" Black
- 77-969 5 1/2" White



twist lock / bases

Cornerstone's classic tapered cage design is elegantly simple, and now its energy efficient, too. Photocells turn energy efficient lamps on and off saving energy costs throughout the year. Available in three finishes, each complemented by Frosted glass panels.



CORNERSTONE ES



Wall Lantern / Arm Up
with photocell

Long & Short Tail Provided
(shown with long tail)

(1) 13W T2 Mini Spiral / GU24 base / 2700K Included

Dimensions: Width 7", Height 12", Extension 9 1/4",
Top to Outlet 11"

60-2201* White / Frosted Glass

60-2202* Old Bronze / Frosted Glass

60-2203* Textured Black / Frosted Glass

Wall Lantern / Arm Up
(shown with short tail)

www.nuvolighting.com

All fixtures CUL wet location listed
except hanging lanterns, (damp location listed).



All Energy Saving
Fixtures Include
GU24 Base CFLs



Wall Lantern / Arm Down with photocell

(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7", Height 13", Extension 9 1/4",
Top to Outlet 4"

60-2204* White / Frosted Glass

60-2205* Old Bronze / Frosted Glass

60-2206* Textured Black / Frosted Glass



Hanging Lantern with photocell

(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7", Height 12 5/8", Chain 48", Wire 12'

60-2207* White / Frosted Glass

60-2208* Old Bronze / Frosted Glass

60-2209* Textured Black / Frosted Glass

Accessories:

25-1166 3' Section of White chain

25-1067 3' Section of Old Bronze chain

25-1071 3' Section of Textured Black chain



Post Lantern with photocell

(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 7", Height 14 1/4"

60-2211 White / Frosted Glass

60-2212 Old Bronze / Frosted Glass

60-2213 Textured Black / Frosted Glass

Accessories:

25-1205 White pier mount base

25-1203 Old Bronze pier mount base

25-1200 Textured Black pier mount base

Styles that recall a simpler time, but updated for today's energy realities, these lanterns are as energy efficient as they are classic. Photocells automatically turn energy efficient lamps on and off for maximum energy savings. Available in three finishes, with Frosted White or Champagne Linen glass.

SMALL WALL LANTERNS ES



www.nuvolighting.com

Onion Lantern with photocell

(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 6", Height 10⁵/₈", Extension 8",
 Top to Outlet 6"
60-3941* White / Frosted Linen Glass
60-3942* Old Bronze / Champagne Linen Glass
60-3943* Textured Black / Frosted Linen Glass

Piper Lantern with photocell

(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
 Dimensions: Width 5", Height 10⁵/₈", Extension 7",
 Top to Outlet 6"
60-3944* White / Frosted Linen Glass
60-3945* Old Bronze / Champagne Linen Glass
60-3946* Textured Black / Frosted Linen Glass





Cube Lantern with photocell

(1) 13W T2 Mini Spiral / GU24 base / 2700K Included
Dimensions: Width 4³/₈", Height 9¹/₂", Extension 6¹/₈",
Top to Outlet 3"

60-2527* White / Frosted Glass

60-2528* Old Bronze / Frosted Glass

60-2529* Textured Black / Frosted Glass

All fixtures CUL wet location listed

small wall lanterns

25-1200	191	60-215	57	60-298	89	60-358	15	60-519	171
25-1203	191	60-216	57	60-299	89	60-359	63	60-520	170
25-1204	191	60-217	57	60-300	45, 53	60-360	38	60-521	170
25-1205	191	60-218	57	60-301	45, 53	60-361	54	60-522	170
25-1206	191	60-219	56	60-302	45, 53	60-362	14	60-523	170
25-1207	191	60-220	56	60-303	45, 53	60-363	62	60-524	170
25-1208	191	60-221	65	60-304	21	60-365	42	60-525	170
25-4021	191	60-222	65	60-305	21	60-366	18	60-526	171
25-4023	191	60-223	65	60-306	21	60-367	58	60-527	171
25-4024	191	60-224	64	60-307	21	60-368	66	60-528	171
25-4025	191	60-225	64	60-308	61	60-370	71	60-529	171
25-4026	191	60-226	64	60-309	61	60-371	71	60-530	171
25-4908	191	60-227	64	60-310	61	60-372	71	60-531	171
25-5605	191	60-228	64	60-311	61	60-373	71	60-532	171
25-5615	191	60-229	73	60-312	69	60-390	42	60-533	171
25-5635	191	60-230	73	60-313	69	60-391	18	60-534	172
25-5645	191	60-231	73	60-314	69	60-392	58	60-535	172
25-5655	191	60-232	73	60-315	69	60-393	66	60-536	172
50-780	190	60-233	73	60-316	88	60-394	42	60-537	172
50-781	190	60-234	73	60-317	88	60-395	18	60-538	172
50-782	190	60-235	72	60-318	88	60-396	58	60-539	172
50-783	190	60-236	72	60-319	88	60-397	66	60-540	166
50-784	190	60-237	73	60-320	43	60-401	158	60-541	166
50-785	190	60-238	73	60-321	43	60-402	158	60-542	166
50-786	190	60-239	73	60-322	43	60-403	158	60-546	167
50-787	190	60-240	73	60-323	43	60-404	158	60-547	167
60-181	39	60-241	73	60-324	19	60-405	158	60-548	167
60-182	39	60-242	73	60-325	19	60-406	158	60-560	171
60-183	15	60-243	72	60-326	19	60-407	158	60-561	171
60-184	15	60-244	72	60-327	19	60-408	158	60-562	171
60-185	55	60-245	82	60-328	59	60-412	159	60-563	171
60-186	55	60-247	82	60-329	59	60-414	159	60-564	170
60-187	63	60-255	58	60-330	59	60-416	159	60-565	170
60-188	63	60-257	42	60-331	59	60-430	159	60-566	170
60-189	39	60-259	18	60-332	67	60-431	159	60-567	170
60-190	39	60-270	42	60-333	67	60-432	159	60-568	170
60-191	15	60-271	42	60-334	67	60-433	159	60-569	170
60-192	15	60-272	18	60-335	67	60-436	159	60-570	171
60-193	55	60-273	18	60-336	88	60-440	156	60-571	171
60-194	55	60-274	58	60-337	88	60-441	156	60-572	171
60-195	63	60-275	58	60-338	88	60-442	156	60-573	171
60-196	63	60-276	66	60-339	88	60-443	156	60-574	171
60-197	41	60-277	66	60-340	44	60-444	156	60-575	171
60-198	41	60-280	17	60-341	44	60-445	156	60-576	171
60-199	41	60-281	17	60-342	44	60-446	156	60-577	171
60-200	40	60-282	17	60-343	44	60-447	156	60-578	172
60-201	40	60-283	41	60-344	20	60-448	156	60-579	172
60-202	40	60-284	41	60-345	20	60-449	156	60-580	172
60-203	40	60-285	41	60-346	20	60-450	156	60-581	172
60-204	40	60-286	65	60-347	20	60-451	156	60-582	172
60-205	17	60-287	65	60-348	60	60-470	176	60-583	172
60-206	17	60-288	65	60-349	60	60-471	176	60-630	168
60-207	17	60-290	88	60-350	60	60-472	176	60-631	168
60-208	16	60-291	43	60-351	60	60-473	176	60-632	168
60-209	16	60-292	19	60-352	68	60-487	167	60-633	168
60-210	16	60-293	59	60-353	68	60-488	167	60-634	168
60-211	16	60-294	67	60-354	68	60-489	167	60-635	168
60-212	16	60-295	82	60-355	68	60-516	171	60-636	169
60-213	57	60-296	89	60-356	39	60-517	171	60-637	169
60-214	57	60-297	89	60-357	55	60-518	171	60-638	169

60-639	169	60-989	165	60-1835	9	60-2623	137	60-3133	122
60-640	169	60-990	165	60-1841	11	60-2624	157	60-3134	122
60-641	169	60-991	165	60-1842	12	60-2625	157	60-3135	121
60-885	163	60-992	165	60-1843	10	60-2627	157	60-3136	121
60-886	163	60-993	165	60-1844	11	60-2628	157	60-3137	121
60-887	163	60-994	165	60-1845	11	60-2629	157	60-3141	31
60-888	162	60-995	165	60-1846	11	60-2631	157	60-3142	31
60-889	162	60-996	165	60-1847	11	60-2632	159	60-3143	31
60-890	162	60-998	155	60-1848	13	60-2633	159	60-3144	31
60-891	162	60-999	155	60-1849	13	60-2634	159	60-3145	33
60-892	162	60-1251	23	60-1851	11	60-2635	159	60-3146	33
60-893	162	60-1252	23	60-1852	13	60-2636	159	60-3147	33
60-894	163	60-1253	23	60-1853	13	60-2637	159	60-3148	32
60-895	163	60-1254	23	60-1854	13	60-2641	80	60-3149	32
60-896	163	60-1255	25	60-1855	13	60-2642	80	60-3151	32
60-897	163	60-1256	25	60-1901	111	60-2643	80	60-3152	32
60-898	163	60-1257	25	60-1902	112	60-2644	80	60-3153	32
60-899	163	60-1258	24	60-1903	110	60-2645	80	60-3154	34
60-900	154	60-1259	24	60-1904	111	60-2646	80	60-3155	35
60-901	154	60-1261	24	60-1905	111	60-2651	157	60-3161	35
60-902	154	60-1262	24	60-1906	111	60-2652	157	60-3162	35
60-903R	154	60-1263	24	60-1907	111	60-2653	157	60-3163	35
60-904R	152	60-1264	27	60-1908	113	60-2654	157	60-3164	35
60-905R	154	60-1265	27	60-1909	113	60-2655	157	60-3165	36
60-906R	152	60-1266	27	60-1911	111	60-2656	157	60-3166	36
60-907	151	60-1267	27	60-1912	113	60-2941	155	60-3167	36
60-908	154	60-1268	27	60-1913	113	60-2942	155	60-3168	36
60-909	154	60-1269	28	60-1914	113	60-2943	155	60-3169	31
60-910	154	60-1271	28	60-1915	113	60-2944	155	60-3171	30
60-911R	154	60-1272	28	60-1921	115	60-2945	155	60-3172	34
60-912R	152	60-1273	28	60-1922	116	60-2946	155	60-3173	34
60-913R	154	60-1274	23	60-1923	114	60-2947	155	60-3174	34
60-914R	152	60-1275	22	60-1924	115	60-2948	155	60-3175	33
60-915	151	60-1276	26	60-1925	115	60-2949	155	60-3176	33
60-916	153	60-1277	26	60-1926	115	60-2951	150	60-3177	33
60-917	153	60-1278	26	60-1927	115	60-3101	119	60-3180	135
60-918	153	60-1279	26	60-1928	117	60-3102	119	60-3181	135
60-919R	153	60-1281	25	60-1929	117	60-3103	119	60-3182	135
60-920R	152	60-1282	25	60-1931	115	60-3104	119	60-3183	135
60-921R	153	60-1283	25	60-1932	117	60-3105	121	60-3184	136
60-922R	152	60-1284	29, 37	60-1933	117	60-3106	121	60-3185	136
60-923	151	60-1285	29, 37	60-1934	117	60-3107	121	60-3186	136
60-924	153	60-1286	29, 37	60-1935	117	60-3108	120	60-3187	136
60-925	153	60-1287	29, 37	60-2201	192	60-3109	120	60-3188	136
60-926	153	60-1290	70	60-2202	192	60-3111	120	60-3189	138
60-927R	153	60-1291	70	60-2203	192	60-3112	120	60-3195	135
60-928R	152	60-1298	70	60-2204	193	60-3113	120	60-3196	134
60-929R	153	60-1821	7	60-2205	193	60-3114	122	60-3197	138
60-930R	152	60-1822	8	60-2206	193	60-3115	123	60-3198	138
60-931	151	60-1823	6	60-2207	193	60-3121	123	60-3199	138
60-936	151	60-1824	7	60-2208	193	60-3122	123	60-3201	137
60-938	151	60-1825	7	60-2209	193	60-3123	123	60-3202	137
60-940	150	60-1826	7	60-2211	193	60-3124	123	60-3203	137
60-944	150	60-1827	7	60-2212	193	60-3125	124	60-3204	140
60-946	150	60-1828	9	60-2213	193	60-3126	124	60-3205	140
60-948	150	60-1829	9	60-2527	195	60-3127	124	60-3206	140
60-985	164	60-1831	7	60-2528	195	60-3128	124	60-3207	140
60-986	164	60-1832	9	60-2529	195	60-3129	119	60-3208	139
60-987	164	60-1833	9	60-2621	137	60-3131	118	60-3209	139
60-988	165	60-1834	9	60-2622	137	60-3132	122	60-3211	139



60-3212	139	60-3321	148	76-024	77	76-501	182	76-657	187
60-3213	139	60-3322	147	76-025	77	76-502	183	76-658	187
60-3240	47	60-3323	147	76-026	77	76-503	183	76-660	72
60-3241	47	60-3324	147	76-091	76	76-505	181	76-661	72
60-3242	47	60-3325	147	76-092	76	76-507	181	76-662	72
60-3243	47	60-3327	147	76-093	76	76-511	181	76-663	72
60-3244	48	60-3331	127	76-124	75	76-513	181	76-664	189
60-3245	48	60-3332	127	76-125	75	76-520	183	76-665	186
60-3246	48	60-3333	127	76-126	75	76-521	183	76-666	186
60-3247	48	60-3334	127	76-127	75	76-522	183	76-667	186
60-3248	48	60-3335	129	76-128	75	76-523	183	76-668	186
60-3249	50	60-3336	129	76-129	75	76-530	183	76-670	80
60-3255	47	60-3337	129	76-130	77	76-531	183	76-671	80
60-3256	46	60-3338	128	76-131	77	76-600	78	76-672	79
60-3257	50	60-3339	128	76-132	77	76-601	79	76-673	80
60-3258	50	60-3341	128	76-133	77	76-602	78	76-674	80
60-3259	50	60-3342	128	76-134	77	76-603	79	76-675	79
60-3261	49	60-3343	128	76-135	77	76-604	78	76-676	80
60-3262	49	60-3344	130	76-191	76	76-605	79	76-677	80
60-3263	49	60-3345	131	76-192	76	76-606	76	76-678	79
60-3264	52	60-3346	125, 133	76-193	76	76-607	76	76-682	183
60-3265	52	60-3347	125, 133	76-243	75	76-608	76	76-683	183
60-3266	52	60-3348	125, 133	76-244	75	76-609	76	76-684	183
60-3271	49	60-3349	125, 133	76-245	75	76-610	76	76-685	183
60-3272	49	60-3351	131	76-246	75	76-611	76	76-690	71
60-3273	49	60-3352	131	76-247	75	76-612	79	76-691	71
60-3277	52	60-3353	131	76-248	75	76-613	79	76-692	71
60-3278	51	60-3354	131	76-250	81	76-614	79	76-693	70
60-3279	51	60-3355	132	76-251	81	76-615	175	76-694	70
60-3281	51	60-3356	132	76-252	81	76-616	174	76-695	70
60-3282	51	60-3357	132	76-253	81	76-617	175	76-700	178
60-3283	51	60-3358	132	76-255	71	76-618	174	76-701	178
60-3290	143	60-3359	127	76-256	82	76-620	175	76-702	178
60-3291	143	60-3361	126	76-257	82	76-621	175	76-703	178
60-3292	143	60-3362	130	76-268	85	76-622	175	76-704	178
60-3293	143	60-3363	130	76-269	85	76-623	175	76-705	178
60-3294	144	60-3364	130	76-270	84	76-624	174	76-747	186
60-3295	144	60-3365	129	76-273	87	76-625	174	76-748	186
60-3296	144	60-3366	129	76-276	87	76-626	174	77-059	78
60-3297	144	60-3367	129	76-277	87	76-627	174	77-060	78
60-3298	144	60-3941	194	76-280	70	76-632	188	77-061	78
60-3299	146	60-3942	194	76-281	70	76-633	188	77-062	78
60-3301	141, 149	60-3943	194	76-282	71	76-634	189	77-086	87
60-3302	141, 149	60-3944	194	76-283	72	76-635	189	77-087	87
60-3303	141, 149	60-3945	194	76-284	72	76-636	189	77-088	87
60-3304	141, 149	60-3946	194	76-412	86	76-637	189	77-097	83
60-3305	143	60-4801	90	76-416	86	76-638	189	77-098	83
60-3306	142	60-4802	90	76-418	86	76-639	189	77-099	83
60-3307	146	60-4803	90	76-422	86	76-640	189	77-100	83
60-3308	146	60-4804	90	76-433	74	76-641	189	77-101	83
60-3309	146	60-5374	20	76-434	74	76-644	189	77-102	83
60-3311	145	60-5375	36	76-435	74	76-645	187	77-108	82
60-3312	145	60-5376	44	76-436	74	76-646	187	77-109	82
60-3313	145	60-5377	52	76-444	70	76-647	187	77-110	82
60-3314	145	60-5378	19	76-445	70	76-648	187	77-111	82
60-3315	145	60-5379	35	76-446	71	76-650	175	77-119	178
60-3316	145	60-5381	43	76-447	71	76-651	175	77-120	87
60-3317	148	60-5382	51	76-448	71	76-652	175	77-121	87
60-3318	148	60-5383	28	76-449	70	76-655	187	77-122	81
60-3319	148	60-5384	27	76-500	182	76-656	187	77-123	81

77-125	81	77-857	173	TH233	100	TH356	103	TP152	106
77-126	84	77-858	173	TH234	100	TH357	103	TP153	106
77-136	177	77-859	173	TH235	100	TH358	103	TP154	106
77-137	177	77-861	173	TH236	100	TH361	103	TP155	106
77-138	177	77-862	179	TH237	100	TH362	103	TP156	107
77-139	177	77-863	176	TH238	100	TH363	103	TP157	107
77-140	177	77-879	176	TH239	100	TH364	103	TP159	105
77-141	177	77-891	176	TH259	101	TH365	103	TP160	105
77-152	177	77-892	173	TH260	101	TH366	103	TP161	105
77-153	177	77-893	173	TH267	101	TH367	103	TP162	105
77-154	177	77-894	173	TH268	101	TH368	103	TP163	105
77-155	177	77-895	173	TH269	101	TH381	104	TP164	105
77-156	177	77-896	180	TH270	101	TH382	104	TP165	105
77-157	177	77-897	180	TH271	101	TH383	104	TP166	105
77-188	89	77-898	180	TH272	101	TH384	104	TP167	107
77-189	89	77-899	180	TH279	99	TH385	104	TP168	107
77-190	89	77-921	79	TH280	99	TH386	104	TP169	106
77-191	89	77-924	79	TH281	99	TK310	95	TP170	106
77-192	89	77-947	82	TH282	99	TK311	95	TP171	106
77-193	89	77-948	82	TH283	99	TK312	95	TP172	106
77-194	89	77-968	191	TH284	99	TK313	95	TP176	105
77-195	89	77-969	191	TH300	98	TK314	95	TP177	105
77-196	89	77-986	78	TH301	98	TK315	95	TP178	105
77-323	188	77-987	78	TH302	98	TK316	92	TP179	105
77-324	188	77-988	79	TH303	96	TK317	92	TP180	105
77-342	83	77-989	87	TH304	97	TK318	92	TP181	105
77-343	83	77-990	87	TH305	96	TK319	92	TP201	107
77-344	83	77-991	87	TH306	97	TK320	92	TP202	106
77-345	78	77-992	178	TH307	96	TK321	92	TP203	106
77-346	78	77-995	178	TH308	97	TK322	92	TP204	106
77-347	78	77-996	178	TH309	100	TK323	92	TP205	107
77-392	84	90-1278	188	TH310	100	TK340	92	TP206	107
77-487	182	90-1279	188	TH311	100	TK341	92	TP207	106
77-488	182	TH200	96	TH312	102	TK342	92	TP208	107
77-494	182	TH201	96	TH313	102	TK343	92	TP209	107
77-495	182	TH202	97	TH314	102	TK345	94	TP211	106
77-530	177	TH203	97	TH315	102	TK346	94	TP231	107
77-531	177	TH204	96	TH316	102	TK347	94	TP232	107
77-532	177	TH205	96	TH317	102	TK348	94	TP233	107
77-533	177	TH206	97	TH321	102	TK349	94	TR118	105
77-692	191	TH207	97	TH322	102	TK352	94	TR119	105
77-693	191	TH208	96	TH323	102	TK353	94	TR120	105
77-700	182	TH209	96	TH324	99	TK354	94	TR121	105
77-701	182	TH210	97	TH327	100	TK355	94	TR122	105
77-702	182	TH211	97	TH328	101	TK361	92	TR123	105
77-703	182	TH216	98	TH331	98	TK362	92	TR124	105
77-726	179	TH217	98	TH332	98	TK381	93	TR125	105
77-727	179	TH218	98	TH333	98	TK382	93	TR126	105
77-728	179	TH219	98	TH341	96	TK383	93	TR127	105
77-729	179	TH220	98	TH342	97	TK384	93	TR128	105
77-748	179	TH221	98	TH343	96	TP142	105	TR129	105
77-749	179	TH222	98	TH344	97	TP143	105	TR131	105
77-750	179	TH223	98	TH345	96	TP144	107	TR132	105
77-751	179	TH224	98	TH346	97	TP145	107	TR133	105
77-823	85	TH225	98	TH347	98	TP146	107	TR134	105
77-824	84	TH226	99	TH348	98	TP147	107		
77-835	176	TH227	99	TH349	98	TP148	106		
77-852	180	TH228	99	TH351	102	TP149	106		
77-853	180	TH229	99	TH352	102	TP150	107		
77-856	179	TH232	100	TH355	103	TP151	107		



index



www.nuvolighting.com
Catalog NU4030
\$10.00



National Toll-Free: **1.800.43.SATCO** (1.800.437.2826) www.satco.com

Corporate Offices & Distribution Center: **NEW YORK** 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027

Distribution Centers: **FLORIDA** 900 N.W. 159th Drive, Miami, FL 33169 800.437.2826 305.624.2044 FAX 305.623.0286
CALIFORNIA 31288 San Benito St. Hayward, CA 94544 800.437.2826 510.487.4822 FAX 510.487.8955
WASHINGTON 4710 116th St. S.W., Mukilteo, WA 98275 800.437.2826 425.789.3300 FAX 425.789.3310
TEXAS 2000 Valwood Parkway, Farmers Branch, TX 75234 800.437.2826 972.247.2437 FAX 972.247.5408
PUERTO RICO Campeche St. 23, Julio N. Matos Industrial Park, Carolina, PR 00984 787.757.3510 FAX 787.757.3540



Like us!



Follow us!

© Copyright 2015, SATCO Products, Inc