



# SATCO

## LIGHT BULBS





SATCO Corporate Headquarters, Brentwood, NY

## Light Bulb Source Book–

We are pleased to present this latest edition of our Light Bulb Source Book. Many new lamps and accessories have been added. Each section is color coded and crafted to locate and identify a specific item in each category with ease.

Satco is committed to providing unsurpassed quality service and produce assortment. Many of our product categories are supported by self stocking merchandising systems and demonstration displays. These efforts, along with many others make Satco the preferred choice in light sources and electrical related products.

Our vast distribution network affords us the unique ability to have the products you want and need in stock and ready to ship from one of our state of the art facilities totaling nearly one million square feet!

## Locations –

- ① Brentwood, New York  
(Corporate Headquarters)
- ② Seattle, Washington
- ③ San Francisco, California
- ④ Dallas, Texas
- ⑤ Miami, Florida
- ⑥ Puerto Rico



## The Complete Satco Product Line



### **The Light Bulb Source Book**

An easy to use catalog sorted by lamp type.



### **The Lamp Specification Catalog**

A technical guide to our lamp selection.



### **General Lighting Products**

Featuring:

- OEM & Consumer Hardware
- Electrical Accessories
- Glassware
- Track & Lighting Fixtures
- Portable Lamps



### **Nuvo Lighting**

Satco's Decorative Lighting Brand



NATIONAL TOLL-FREE  
1-800-43-SATCO (1-800-437-2826)

**NEW YORK EXECUTIVE OFFICES & WAREHOUSE:**  
110 Heartland Blvd.  
Brentwood, N.Y. 11717  
800-437-2826  
(631) 243-2022  
FAX:(631) 243-2027

**FLORIDA**  
900 N.W. 159th Drive  
Miami, Florida 33169  
800-437-2826  
(305) 624-2044  
FAX:(305) 623-0286

**TEXAS**  
2000 Valwood Parkway  
Farmers Branch,  
Texas 75234  
800-437-2826  
(972) 247-2437  
FAX:(972) 247-5408

**CALIFORNIA**  
31288 San Benito St.  
Hayward, California 94544  
800-437-2826  
(510) 487-4822  
FAX:(510) 487-8955

**WASHINGTON**  
4710 116th St. S.W.  
Mukilteo,  
Washington 98275  
800-437-2826  
(425) 789-3300  
FAX:(425) 789-3310

**PUERTO RICO**  
Bldg 3, Compeche St. 22  
Julio N. Matos Industrial Park  
Bo Martin Gonzales  
Carolina, PR 00984  
800-437-2826  
(787) 757-3510  
FAX:(787) 757-3540

www.satco.com

the  
**SATCO**  
advantage

### **Six fully inventoried distribution centers.**

Each Satco facility features the latest warehouse management systems ensuring that each order is addressed in a timely and efficient manner.

### **Comprehensive product selection we have what you need.**

Our unique product offering positions us as a "One Shop" vendor. Satco has compiled a variety products through various industry relationships which makes us the primary choice for selection and service.

### **Products produced to the highest industry standards.**

Quality products – An adage we've built our company by. Every item we sell has been designed, produced and tested to meet or exceed industry benchmarks for quality and testing. Quality assurance is controlled on all levels from production to shipping.

### **Innovative technology.**

Satco owns numerous patents on lamp and lighting technology. As a leader we have introduced many new concepts that have been embraced by the lighting community.

### **Retail packaging and merchandising programs.**

Satco's product assortment includes many retail point of purchase items packaged for the consumer market. These product programs are supported by eye-catching easy to use merchandisers

### **Forty years of performance.**

A proven history of service, quality and relationships are the integral part of who we are. We value our long term associations and looking forward to many more successful years together.

### **Exceptional customer service.**

The backbone of any company is their customer service. Each of our distribution centers are staffed with highly experienced knowledgeable personnel ready to assist. If you can't locate an item you are looking for, just ask – chances are we have it!

# LAMPS

*at a glance*

## **Incandescent Lamps**

### **Advantages**

- Low initial cost
- Low fixture cost
- Simple installation
- Inexpensive to dim
- All-weather operation
- High CRI

### **Disadvantages**

- Voltage sensitive
- Lowest efficacy
- Short life
- Heat

## **Tungsten Halogen**

### **Advantages**

- Whiter light than incandescent
- Excellent lumen maintenance
- Longer life than incandescent
- More efficient than incandescent

### **Disadvantages**

- More costly than incandescent

## **Fluorescent Lamps**

### **Advantages**

- High efficacy
- Very good color
- Wide range of colors
- Good lumen maintenance
- Long life

### **Disadvantages**

- Temperature effects
- Requires a ballast
- Light control

## **Mercury Vapor**

### **Advantages**

- Good for landscape lighting
- Long life
- All-weather operation

### **Disadvantages**

- Lowest HID efficacy
- Poor lumen maintenance
- Poor color
- Requires a ballast
- Restrike time

## **High Pressure Sodium**

### **Advantages**

- Highest efficacy
- Long life
- Universal burning position
- Range of wattages
- Good lumen maintenance
- All-temperature operation

### **Disadvantages**

- Color
- Requires a ballast
- Cycling (standard lamp)

## **Metal Halide**

### **Advantages**

- High efficacy
- Good color
- Good lumen maintenance
- Wide range of wattages
- Medium-long life
- All-temperature operation

### **Disadvantages**

- Color shift
- Hot restrike time
- Requires a ballast

# GLOSSARY

*of terms*

## **Ampere**

A unit of measurement which expresses the rate of flow of electricity.

## **Average Rated Life**

An average rating, in hours indicating when half of a large group of lamps have failed, when operated at rated lamp voltage and current.

## **Ballast**

A device used with a discharge lamp to obtain the necessary voltage for starting and operating.

## **Center Beam Candlepower (CBCP)**

The intensity of light produced at the center of a reflector lamp, expressed in candelas.

## **Color Rendering Index (CRI)**

The measure of a light source to render color correctly.

## **Lamp**

A manufactured light source. The three main categories are: incandescent, Fluorescent and HID (high intensity discharge).

## **Light**

Radiant energy that is capable of producing a visual light.

## **Maximum Overall Length (MOL)**

The total length of a lamp from the top of bulb to the bottom of the base.

## **Power Factor**

A measure of the effectiveness with which a device converts volt-amperes to watts.

## **Total Harmonic Distortion (THD)**


The rating which expresses the ability of a ballast not to affect the frequency.

## **Voltage**

The measurement of electrical potential expressed in volts (V).

# Reference Guide

## Lamp Logic



**Size:** Incandescent bulb size is determined by the bulb's maximum diameter ( the diameter at it's widest part). This measurement is always expressed in eighths of an inch.

**For example;** an A19 bulb's maximum diameter is 19 eighths of an inch or 19/8" or 2 3/8".


A G40 bulb is 40 / 8" or 5" .

Following are some examples of popular bulb shapes.


## Bulb Shapes

The size and shape of a bulb is designated by a letter code followed by a number. The letter indicates the shape of the bulb and the number indicates the diameter in eighths of an inch.


### Incandescent Bulb Shapes



### Miniature Lamps




### Base Types




## Reference Guide

product reference guide


### HID Bulb Shapes



### Compact Fluorescent Bulb Shapes



### Compact Fluorescent Bases



<b>Color Temp.</b>	Warm	Neutral	Cool	Daylight
<b>Kelvin Range</b>	3000K	3500K	4100K	5000K
<b>Effect &amp; Moods</b>	Warm & Friendly	Inviting & Comfortable	Clean & Organized	Bright & Alert
<b>Application</b>	Homes & Restaurants	Showrooms & Reception Areas	Office & Hospitals	Galleries & Jewelry Display



## Color Application Guide

## Color Rendering

## Lamp Color



The Color Rendering Index is based on a maximum rating of 100. Light sources with a low CRI will make objects appear washed out and dull. Lamps with high CRI ratings will be more vivid and bring life to the subject.


The color of light is based on a color temperature scale which is rated in Kelvins. A warm color of light would be in 2000 - 3000K range and would make the red, orange and yellow colors more predominant. Light sources with a color temperature in the 4000K range would feature more blue or cool colors. The photographs shown here illustrate how the color of a light source can impact the appearance of objects.

## Color Matching

Choose from a wide assortment of color temperatures to match different lamp types in an application.

Many of the light sources shown throughout the catalog offer a wide range of color options to suit your specific design needs.

## Fluorescent Bulb Shapes



# Table of Contents



table of contents

## REFLECTORS




### Reflectors

R14 & R16	14
K19	21
R20 & BR25	15
BR30	16-18
BR40	19
ER30 & ER40	25
R20/BR30/BR40 Halogen	20
Plant Light Reflectors	24
BR38 Floods	25




### Color Reflectors

R20 Colors	22
BR30 Colors	23
BR38 Colors	27



### PAR Reflectors

Incandescent PARs	29-30
Soft Ray PARs	31
PAR14-PAR38 Halogen	32-36



### Heat Lamps

BR38 Red	28
R40 Clear	28
R40 Red	28

## DECORATIVE INCANDESCENT LAMPS



### Globe Lights

G8 & G12 Globe Lights	40
G12 Colored Globe Lights	41
G16½ Silver Crown	41
G16½ Globe Lights	42-43
G14 & G17 Globe Lights	44
G16½ & G18½ Med.	45
G25 Globe Lights	46-49
G25 Silver Crown	50
G40 Globe Lights	51



### Decorative Bulbs

Chandelier Bulbs 120V	52-56
Chandelier Bulbs 130V	57-61
Petite & Specialty	62-63
F10 & F15 Flame	64
Krypton G16½, Torp. Flame	65
Satco-Escent®	66-67
Flicker Bulbs	68
Prismatics Bulbs	69
Colored Torpedo	70

## GENERAL SERVICE LAMPS



Night Light Bulbs	74
Display/Sign Bulbs	75
Tubular	76-78
Hi-Intensity	79
Appliance/Indicators	80-81
A15	82-83
A19 2 Pack	84-85
A19 4 Pack	86
A19 Black Light/Bug/Silver Cr.	88
A19 Party Bulbs	89-91



A19 EconoBrite™	92-93
A19 Energy Saver	102
A19/A21/A23 Commercial Serv.	87
A19 Safety Coated	94
A21 Safety Coated	95
A19 Rough Service	95
3-Way	96-97
A21 Household	98
A23 Household	99
PS25/PS35	100-101



# Table of Contents

## SPECIALTY LAMPS



Linear Incandescent .....106  
Neodymium Lamps .....107-109  
Shatter-Proof .....110-111  
A19 Low Voltage .....112



Export A19 130V-230V .....113  
Export G25 220V .....114  
Export Decorative 220V .....115  
Export Reflectors 230V .....114

## HALOGEN LAMPS



PAR14~PAR38 Halogen ..120-124  
Soft Ray PARs .....125  
R20/BR30/BR40 Halogen ....126  
MR8/MR11 12V & 24V .....127  
MR16 120V .....128  
MR16 12V & 24V .....129-131  
ALR .....132  
AR70/AR111 .....133  
PAR36/PAR 56/PAR64 .....134



General Service .....135  
JD Bayonet .....136  
JD Mini-Can .....137  
JD Euro .....137  
T3 Krypton/Xenon .....138  
Capsules 12V/24V/120V .....139  
J-Type .....140  
Ball Lite .....141  
A-Type .....142

## CARDED LAMPS



Chandelier Bulbs 120V ..146-151  
Chandelier Bulbs 130V ..152-156  
Globe .....157-159  
Satco-Escent® .....160  
F10 & F15 Flame .....161-162  
Krypton/Diamond Cut .....163  
Silicone Tip .....163  
Ceiling Fan Bulbs .....164  
Prismatic Bulbs .....165  
Flicker Bulbs .....166



Tubular .....167  
Hi-Intensity/Sign .....168  
R14 &R16 Reflectors .....171  
MR11 & MR16 .....172  
JD E11/E14/BA15D .....173  
Capsules 12V/120V .....174  
GU10/JDR .....175  
Double Envelope .....175  
J Type .....176-177  
Compact Fluorescent .....178

## FLUORESCENT LAMPS



T2-T8 Linear Tubes .....182-188  
T8 U Bend Tubes .....189  
T12 Linear Tubes .....190-192  
T12 U Bend Tubes .....193  
T6/T8/T12 Slimline Tubes .194-195  
T12 HO/VHO Tubes .....196-197  
T5/T9 Circline Tubes ....198-199  
Shatterproof Lamps .....200-201  
Pin Based Compact ....202-213



### Self Ballasted

Mini Spiral CFL .....214  
Standard Spiral CFL .....215  
R20~R40/BR38 CFL .....216  
A Type CFL .....219  
Torpedo/Bullet/Globe CFL ....220  
Spiral w/Photocell CFL .....221  
Bug CFL .....221  
Circline .....222

# Table of *Contents*



table of contents

## HID LAMPS



### Metal Halide

Mogul Base . . .226-229,232-233  
 Medium Base . . . . .226-229  
 PAR Type . . . . .230  
 R40 Reflector . . . . .230  
 Double Ended . . . . .231  
 Single Ended T Type . . . . .231  
 Double Ended T Type . . . . .231



### Mercury Vapor

Mogul Base . . . . .234-235  
 Medium Base . . . . .235  
High Pressure Sodium  
 Medium Base . . . . .236  
 Mogul Base . . . . .237-239  
Low Pressure Sodium  
 Sox Lamps . . . . .240

## SEALED BEAM LAMPS



### Screw Terminal

PAR36 . . . . .244  
 PAR46 . . . . .245



### Mogul End Prong

PAR56. . . . .246  
 PAR64. . . . .246

## MINIATURE & SPECIALTY LAMPS



### Incandescent

B-3½, G-3½, G-4½ . . . . .252  
 G-6, B-6, T-5 . . . . .253  
 S-8, RP11 . . . . .254



### Xenon

T-3¼, T5 Wedge . . . . .255  
 T-3¼ Double End Cap . . . . .256  
 RLX . . . . .256

## BALLASTS & ACCESSORIES



### Ballasts

Electronic . . . . .260-262  
 Magnetic . . . . .263-264  
 Socket Ballasts . . . . .265



### Accessories

Bulb Changers . . . . .266  
 Bulb Cages . . . . .266  
 Bulb Extenders . . . . .266

## R14 & R16

1500 Hours

Not Shown Actual Size



**R14**  
Intermediate Base  
120 Volt  
**S3205** 25 Watt  
**S3215** 40 Watt



**R14**  
E14/Euro. (Mignon) Base  
130 Volt  
**S3396** 40 Watt



**R16**  
Medium Base  
120 Volt  
**S3214** 40 Watt



**Shortneck R14**  
Medium Base  
120 Volt  
**S3601** 25 Watt  
**S3602** 40 Watt



**R14**  
Medium Base  
120 Volt  
**S3604** 25 Watt  
**S3605** 40 Watt

Packing:  
Individually Boxed  
500/Master, 25/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
25	R14	Int.	<b>S3205</b>	25R14N	Lt. Frost	120V	1500	135	CC2V	2 5/8"	Box	500/25
25	R14	Med.	<b>S3601</b>	25R14	Lt. Frost	120V	1500	135	CC2V	2 1/4"	Box	500/25
25	R14	Med.	<b>S3604</b>	25R14	Lt. Frost	120V	1500	135	CC2V	2 5/8"	Box	500/25
40	R14	E14/Euro	<b>S3396</b>	40R14	Lt. Frost	130V	1500	280	CC2V	2 5/8"	Box	500/25
40	R14	Int.	<b>S3215</b>	40R14N	Lt. Frost	120V	1500	280	CC2V	2 5/8"	Box	500/25
40	R14	Med.	<b>S3602</b>	40R14	Lt. Frost	120V	1500	280	CC2V	2 1/4"	Box	500/25
40	R14	Med.	<b>S3605</b>	40R14	Lt. Frost	120V	1500	280	CC2V	2 5/8"	Box	500/25
40	R16	Med.	<b>S3214</b>	40R16	Frost	120V	1500	280	C-9	3 7/16"	Box	500/25

**R20 & BR25**

**2000 Hours**

*Not Shown Actual Size*

**R20**

Medium Base

120 Volt

**S3210** 30 Watt

**S3204** 50 Watt

**S3211** 75 Watt

**S3226** 100 Watt

**S2810** 30 Watt/130 Volt

**S3804** 50 Watt/130 Volt

**S2811** 75 Watt/130 Volt

Packing:

Individually Sleeved

96/Master

12/Inner



**BR25**

Medium Base

120 Volt

**S2806** 65 Watt

**S2807** 85 Watt

Packing:

Individually Sleeved

96/Master

12/Inner



reflectors

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
30	R20	Med.	<b>S3210</b>	30R20	Frost	120V	2000	185	CC-9	4"	Sleeve	96/12
30	R20	Med.	<b>S2810</b>	30R20/130	Frost	130V	2000	185	CC-9	4"	Sleeve	96/12
50	R20	Med.	<b>S3204</b>	50R20	Frost	120V	2000	375	CC-9	4"	Sleeve	96/12
50	R20	Med.	<b>S3804</b>	50R20/130	Frost	130V	2000	375	CC-9	4"	Sleeve	96/12
75	R20	Med.	<b>S3211</b>	75R20	Frost	120V	2000	690	CC-9	4"	Sleeve	96/12
75	R20	Med.	<b>S2811</b>	75R20/130	Frost	130V	2000	690	CC-9	4"	Sleeve	96/12
100	R20	Med.	<b>S3226</b>	100R20	Frost	120V	2000	925	CC-9	4"	Sleeve	96/12
65	BR25	Med.	<b>S2806</b>	65BR25/FL	Frost	120V	2000	600	CC-6	4 3/4"	Sleeve	96/12
85	BR25	Med.	<b>S2807</b>	85BR25/FL	Frost	120V	2000	800	CC-6	4 3/4"	Sleeve	96/12

## BR30

2000 Hours

Not Shown Actual Size

### BR30

Medium Base

**S3259** 50 Watt

**S2808** 65 Watt

**S3408** 65 Watt/130 Volt

**S2809** 85 Watt

**S3409** 85 Watt/130 Volt

Packing: Individually Sleeved  
96/Master, 12/Inner



Colorful  
Multi Pack  
Inner Cartons

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack Type	Mst.Ctn./ Inner Pack
50	BR30	Med.	<b>S3259</b>	50BR30/FL	Frost	120V	2000	550	CC-9	5 3/8"	Sleeve	96/12
65	BR30	Med.	<b>S2808</b>	65BR30/FL	Frost	120V	2000	685	CC-9	5 3/8"	Sleeve	96/12
65	BR30	Med.	<b>S3408</b>	65BR30/FL	Frost	130V	2000	685	CC-9	5 3/8"	Sleeve	96/12
85	BR30	Med.	<b>S2809</b>	85BR30/FL	Frost	120V	2000	925	CC-9	5 3/8"	Sleeve	96/12
85	BR30	Med.	<b>S3409</b>	85BR30/FL	Frost	130V	2000	925	CC-9	5 3/8"	Sleeve	96/12

*2000 Hours*

2 Pack **BR30**



*Not Shown Actual Size*

**BR30/2 Pack**

Medium Base

**S2817** 65 Watt

**S3417** 65 Watt/130 Volt

Packing: 2/Box

60 2-Packs /Master

*Sold Per Pack*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn.
65	BR30	Med.	<b>S2817</b>	65BR30/FL/2PK	Frost	120V	2000	685	CC-9	5 3/8"	Box/2	60/2
65	BR30	Med.	<b>S3417</b>	65BR30/FL/2PK	Frost	130V	2000	685	CC-9	5 3/8"	Box/2	60/2

## BR30

5000 Hours

**BR30**  
 Long Life  
 Commercial Grade

Medium Base  
 130 Volt

**S6208** 65 Watt/130 Volt  
 Packing: Individually Sleeved  
 24/Master



Not Shown Actual Size


Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
65	BR30	Med.	<b>S6208</b>	65BR30/FL/LL	Frost	130V	5000	532	CC-9	5 3/8"	Sleeve	24

**2500 Hours**

*Not Shown Actual Size*



**LONGER LIFE!**



**BR40**

Medium Base

**S2853** 65 Watt

**S4453** 65 Watt/130 Volt

**S2854** 85 Watt/120-130 Volt

**S2855** 120 Watt

**S4455** 120 Watt/130 Volt

Packing: Individually Sleeved  
24/Master

reflectors

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated		Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn.
						Volts	Hours					
65	BR40	Med.	<b>S2853</b>	65BR/FL	Frost	120V	2500	685	CC-6	6 1/2"	Sleeve	24
65	BR40	Med.	<b>S4453</b>	65BR/FL	Frost	130V	2500	685	CC-6	6 1/2"	Sleeve	24
85	BR40	Med.	<b>S2854</b>	85BR/FL	Frost	120-130V	2500	925	CC-6	6 1/2"	Sleeve	24
120	BR40	Med.	<b>S2855</b>	120BR/FL	Frost	120V	2500	1150	CC-6	6 1/2"	Sleeve	24
120	BR40	Med.	<b>S4455</b>	120BR/FL	Frost	130V	2500	1150	CC-6	6 1/2"	Sleeve	24



# Halogen Reflectors



## R20/BR30/BR40

2500 Hours

- Nickel Plated Brass Base
- High Lumen Output
- Brilliant White Light
- Better Color Rendering than Standard Floods
- 20% Brighter & Longer Lasting



reflectors

### R20

Medium Base  
120 Volt  
**S4500** 50 Watt  
Packing: Individually Sleeved  
48/Master, 6/Inner

### BR30

Medium Base  
120 Volt/130Volt  
**S4501** 60 Watt  
**S4401** 60 Watt/130 Volt  
**S4502** 75 Watt  
**S4402** 75 Watt/130 Volt  
Packing: Individually Sleeved  
48/Master, 6/Inner

### BR40

Medium Base  
120 Volt  
**S4504** 75 Watt  
**S4503** 100 Watt  
Packing: Individually Sleeved  
24/Master, 6/Inner

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Lumens	Kelvin	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
50	R20	Med.	<b>S4500</b>	50R20/FL/HAL	70°	120V	2500	480	3000K	4"	Sleeve	48/6
60	BR30	Med.	<b>S4501</b>	60BR30/FL/HAL	80°	120V	2500	730	3000K	5 3/8"	Sleeve	48/6
60	BR30	Med.	<b>S4401</b>	60BR30/FL/HAL	80°	130V	2500	730	3000K	5 3/8"	Sleeve	48/6
75	BR30	Med.	<b>S4502</b>	75BR30/FL/HAL	80°	120V	2500	900	3000K	5 3/8"	Sleeve	48/6
75	BR30	Med.	<b>S4402</b>	75BR30/FL/HAL	80°	130V	2500	900	3000K	5 3/8"	Sleeve	48/6
75	BR40	Med.	<b>S4504</b>	75BR40/FL/HAL	90°	120V	2500	900	3000K	6 1/2"	Sleeve	24/6
100	BR40	Med.	<b>S4503</b>	100BR40/FL/HAL	90°	120V	2500	1400	3000K	6 1/2"	Sleeve	24/6

*1500 Hours*

2 Pack **K19**



Satco **K19** directional reflector lamps are specifically designed to create a soft, glare free light source.

*Not Shown Actual Size*

*Directional Reflectors*

*White*

*Medium Base  
120 Volt*

**S4976** 40 Watt

**S4977** 60 Watt

**S4978** 75 Watt

**S4979** 100 Watt

*Packing: 2/Box, 12/2 Packs*

*Sold Per Pack*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn.
40	K19	Med.	<b>S4976</b>	40K19/2PK	White	120	1500	260	C-9	4 1/8"	Box/2	12
60	K19	Med.	<b>S4977</b>	60K19/2PK	White	120	1500	520	C-9	4 1/8"	Box/2	12
75	K19	Med.	<b>S4978</b>	75K19/2PK	White	120	1500	680	C-9	4 1/8"	Box/2	12
100	K19	Med.	<b>S4979</b>	100K19/2PK	White	120	1500	1000	C-9	4 1/8"	Box/2	12

reflectors

# Reflectors *Brass Base*



## R20 colors

130 Volt 2000 Hours

Not Shown Actual Size

Medium Base 130 Volt  
Packing: Individually Sleeved  
96/Master, 12/Inner



**S3200** 50 Watt Red



**S3201** 50 Watt Green



**S3202** 50 Watt Blue



**S3203** 50 Watt Amber



**S3212** 50 Watt Pink

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
50	R20	Med.	<b>S3200</b>	50R20/R	Red	130	2000	n/a	C-9	4"	Sleeve	96/12
50	R20	Med.	<b>S3201</b>	50R20/G	Green	130	2000	n/a	C-9	4"	Sleeve	96/12
50	R20	Med.	<b>S3202</b>	50R20/B	Blue	130	2000	n/a	C-9	4"	Sleeve	96/12
50	R20	Med.	<b>S3203</b>	50R20/A	Amber	130	2000	n/a	C-9	4"	Sleeve	96/12
50	R20	Med.	<b>S3212</b>	50R20/PK	Pink	130	2000	n/a	C-9	4"	Sleeve	96/12

reflectors

*2000 Hours 130 Volt*

**BR30** colors



**S3227** 75 Watt Green



**S3240** 75 Watt Red

*Not Shown Actual Size*

*Medium Base 130 Volt  
Packing: Individually Sleeved  
96/Master, 12/Inner*



**S3213** 75 Watt Pink



**S3239** 75 Watt Amber



**S3228** 75 Watt Blue

reflectors

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
75	BR30	Med.	<b>S3240</b>	75BR30/R	Red	130	2000	n/a	C-9	5 3/8"	Sleeve	96/12
75	BR30	Med.	<b>S3227</b>	75BR30/G	Green	130	2000	n/a	C-9	5 3/8"	Sleeve	96/12
75	BR30	Med.	<b>S3228</b>	75BR30/B	Blue	130	2000	n/a	C-9	5 3/8"	Sleeve	96/12
75	BR30	Med.	<b>S3239</b>	75BR30/A	Amber	130	2000	n/a	C-9	5 3/8"	Sleeve	96/12
75	BR30	Med.	<b>S3213</b>	75BR30/PK	Pink	130	2000	n/a	C-9	5 3/8"	Sleeve	96/12

# Plant Light *Brass Base*



## Reflectors

120 Volt / 2000 Hours

Not Shown Actual Size



### R20/R25/R30

#### Plant Lights

Medium Base

120 Volt

**S2850** 50 Watt/R20

**S2851** 75 Watt/R25

**S2852** 150 Watt/R30

Packing: Individually Boxed  
96/Master, 12/Inner



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
50	R20	Med.	<b>S2850</b>	50R20/Plant	120V	2000	n/a	C-9	4"	Box	96/12
75	R25	Med.	<b>S2851</b>	75R25/Plant	120V	2000	n/a	C-9	4 3/4"	Box	96/12
150	R30	Med.	<b>S2852</b>	150R30/Plant	120V	2000	n/a	C-9	5 3/8"	Box	96/12

reflectors

**2000 Hours**

**ER30 & ER40**

*Elliptical Reflectors produce more useable light beyond the lamp surface. They are perfect for use in deeply recessed fixtures.*



**ER30**

**Elliptical**

Medium Base

130 Volt

**S4956** 50 Watt

**S4957** 75 Watt

Packing:

Individually Sleeved  
24/Case

**ER40**

**Elliptical**

Medium Base

130 Volt

**S4958** 120 Watt

Packing:

Individually Sleeved  
24/Case

*Not Shown  
Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
50	ER30	Med.	<b>S4956</b>	50ER30	Frost	130V	2000	310	CC6	6 1/8"	Sleeve	24
75	ER30	Med.	<b>S4957</b>	75ER30	Frost	130V	2000	620	CC6	6 1/8"	Sleeve	24
120	ER40	Med.	<b>S4958</b>	120ER40	Frost	130V	2000	1180	CC6	7 1/4"	Sleeve	24

# Reflectors *Brass Base*



## **BR38** Weatherproof

**2000 Hours**

**BR38** Medium Base  
120 Volt /130 Volt

**S4420** 75 Watt

**S4430** 75 Watt/130 Volt

**S4421** 150 Watt

**S4431** 150 Watt/130 Volt

Packing: Individually Boxed  
12/Master

**S4422** 75 Watt (2 Pack)

**S4423** 150 Watt (2 Pack)

Packing: 2 per Box

8 2pk/Master

Sold Per Pack



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn.
75	BR38	Med.	<b>S4420</b>	75BR38/FL	Clear	120V	2000	700	CC9	5 5/16"	Box	12
75	BR38	Med.	<b>S4430</b>	75BR38/FL	Clear	130V	2000	700	CC9	5 5/16"	Box	12
75	BR38	Med.	<b>S4422</b>	75BR38/FL/2PK	Clear	120V	2000	700	CC9	5 5/16"	Box/2	8
150	BR38	Med.	<b>S4421</b>	150BR38/FL	Clear	120V	2000	1550	CC9	5 5/16"	Box	12
150	BR38	Med.	<b>S4431</b>	150BR38/FL	Clear	130V	2000	1550	CC9	5 5/16"	Box	12
150	BR38	Med.	<b>S4423</b>	150BR38/FL/2PK	Clear	120V	2000	1550	CC9	5 5/16"	Box/2	8

*2000 Hours*

**BR38** Weatherproof



**S4424** 100 Watt Red



**S4425** 100 Watt Amber

**BR38**  
Colors

Medium Base  
120 Volt  
Packing:  
Individually Boxed  
6/Master



**S4426** 100 Watt Yellow



**S4427** 100 Watt Green



**S4428** 100 Watt Blue



**S4429** 100 Watt Pink

*Not Shown*  
*Actual Size*

reflectors

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
100	BR38	Med.	<b>S4424</b>	100BR38/R	Red	120V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	Med.	<b>S4425</b>	100BR38/A	Amber	120V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	Med.	<b>S4426</b>	100BR38/Y	Yellow	120V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	Med.	<b>S4427</b>	100BR38/G	Green	120V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	Med.	<b>S4428</b>	100BR38/B	Blue	120V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	Med.	<b>S4429</b>	100BR38/PK	Pink	120V	2000	n/a	CC9	5 5/16"	Box	6



## Heat lamps

5000 Hours



**R40/Clear**  
Infrared Heat Lamp  
Medium Base (120 Volt)  
**S4999** 250 Watt Clear

Packing: Individually Sleeved, 12/Master



**R40/Red**  
Infrared Heat Lamp  
Medium Base (120 Volt)  
**S4998** 250 Watt Red

Packing: Individually Sleeved, 12/Master



**BR38/Red**  
Infrared Heat Lamp  
Medium Base (120 Volt)  
**S4751** 175 Watt Red

Packing: Individually Boxed, 12/Master



**R40/Clear**  
Infrared Heat Lamp  
Medium Base (120 Volt)  
**S4750** 125 Watt Clear

Packing: Individually Boxed, 12/Master

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
125	R40	Med.	<b>S4750</b>	125R40/1	Clear	120V	5000	n/a	C-9	6 1/2"	Box	12
175	BR38	Med.	<b>S4751</b>	175BR38/HR	Red	120V	5000	n/a	C-9	5 5/16"	Box	12
250	R40	Med.	<b>S4999</b>	250R40/1	Clear	120V	5000	n/a	C-9	6 1/2"	Sleeve	12
250	R40	Med.	<b>S4998</b>	250R40/HR	Red	120V	5000	n/a	C-9	6 1/2"	Sleeve	12

# Brass Base Reflectors

## PAR38

2 Piece Construction

Weatherproof



Shown Actual Size

### PAR38

Medium Base,  
2 Piece Construction

**S4952** 65 Watt Flood

**S4953** 65 Watt Flood/130 Volt

**S4951** 65 Watt Spot

**S4954** 150 Watt Flood/130 Volt

**S4955** 150 Watt Spot/130 Volt

Packing: Individually Boxed  
15/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Lumens	CBCP	Filament	M.O.L.	Pack. Type	Mst.Ctn.
65	PAR38	Med. Skt.	<b>S4952</b>	65PAR/FL	Flood 30°	120V	1750	715	1700	CC-6	5 5/16"	Box	15
65	PAR38	Med. Skt.	<b>S4953</b>	65PAR/FL/130	Flood 30°	130V	1750	715	1700	CC-6	5 5/16"	Box	15
65	PAR38	Med. Skt.	<b>S4951</b>	65PAR/SP	Spot 12°	120V	1750	715	5500	CC-6	5 5/16"	Box	15
150	PAR38	Med. Skt.	<b>S4954</b>	150PAR/FL/130	Flood 30°	130V	750	2175	4500	CC-6	5 5/16"	Box	15
150	PAR38	Med. Skt.	<b>S4955</b>	150PAR/SP/130	Spot 12°	130V	750	2175	18000	CC-6	5 5/16"	Box	15

#### 130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE

57	PAR38	Med. Skt.	<b>S4953</b>	65PAR/FL/130	Flood 30°	130V	4375	540	1285	CC-6	5 5/16"	Box	15
132	PAR38	Med. Skt.	<b>S4954</b>	150PAR/FL/130	Flood 30°	130V	1875	1660	3435	CC-6	5 5/16"	Box	15
132	PAR38	Med. Skt.	<b>S4955</b>	150PAR/SP/130	Spot 12°	130V	1875	1660	13735	CC-6	5 5/16"	Box	15

# PAR Reflectors

## PAR36/PAR38/PAR56

Not Shown Actual Size



### PAR38 Side Prong

#### 2 Piece Construction

Side Prong Base,

**S4800** 75 Watt Flood

**S4801** 75 Watt Spot

**S4675\*** 90 Watt Halogen Flood

**S4674\*** 90 Watt Halogen Spot

**S4802** 150 Watt Flood

**S4803** 150 Watt Spot

Packing: Individually Boxed

12/Master

\*15/Master



### PAR36 12 Volt Screw Terminal

#### INCANDESCENT

**S4804** 50 Watt PAR36 Wide Flood

**S4805** 50 Watt PAR36 Narrow Spot

#### HALOGEN

**S4809** 36 Watt PAR36 Wide Flood

**S4808** 36 Watt PAR36 Narrow Spot

**S4807** 36 Watt PAR36 Very Narrow Spot

**S4806** 50 Watt PAR36 Narrow Spot

Packing: Individually Boxed

12/Master

### PAR56 120 Volt Mogul Side Prong

#### INCANDESCENT

**S4810** 300 Watt PAR56 Medium Flood

**S4811** 300 Watt PAR56 Wide Flood

**S4963** 300 Watt PAR56 Narrow Spot

Packing: Individually Boxed

12/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn.
75	PAR38	Side Prong	<b>S4800</b>	75PAR/3FL/MINE	Flood 30°	120V	2000	1750	765	CC-6	4 5/16"	Box	12
75	PAR38	Side Prong	<b>S4801</b>	75PAR/3SP/MINE	Spot 15°	120V	2000	5900	765	CC-6	4 5/16"	Box	12
90	PAR38	Side Prong	<b>S4675</b>	90PAR/CAP/3FL	Flood 30°	120V	2500	3500	1310	CC-8	4 5/16"	Box	15
90	PAR38	Side Prong	<b>S4674</b>	90PAR/CAP/3SP	Spot 12°	120V	2500	14300	1310	CC-8	4 5/16"	Box	15
150	PAR38	Side Prong	<b>S4802</b>	150PAR/3FL/MINE	Flood 30°	120V	2000	3600	1740	CC-6	4 5/16"	Box	12
150	PAR38	Side Prong	<b>S4803</b>	150PAR/3SP/MINE	Spot 18°	120V	2000	9200	1740	CC-6	4 5/16"	Box	12
50	PAR36	Screw Term.	<b>S4804</b>	50PAR36/WFL	Flood 35°	12V	2000	720	330	C-6	2 3/4"	Box	12
50	PAR36	Screw Term.	<b>S4805</b>	50PAR36/NSP	Spot 8°	12V	2000	11000	330	C-6	2 3/4"	Box	12
36	PAR36	Screw Term.	<b>S4809</b>	36PAR36/CAP/WFL	Flood 32°	12V	4000	1000	500	C-8	2 3/4"	Box	12
36	PAR36	Screw Term.	<b>S4808</b>	36PAR36/CAP/NSP	Spot 13°	12V	4000	3500	500	C-8	2 3/4"	Box	12
36	PAR36	Screw Term.	<b>S4807</b>	36PAR36/CAP/VNSP	Spot 5°	12V	4000	17000	500	C-8	2 3/4"	Box	12
50	PAR36	Screw Term.	<b>S4806</b>	50PAR36/CAP/NSP6	Spot 6°	12V	4000	25000	700	C-8	2 3/4"	Box	12
300	PAR56	Mog End Prong	<b>S4810</b>	300PAR56/MFL	Flood 23°	120V	2000	24000	3840	CC-13	5"	Box	12
300	PAR56	Mog End Prong	<b>S4811</b>	300PAR56/WFL	Flood 37°	120V	2000	11000	3840	CC-13	5"	Box	12
300	PAR36	Mog End Prong	<b>S4963</b>	300PAR56/NSP	Spot 10°	120V	2000	68000	3840	CC-13	5"	Box	12

# SATCO® SOFTRAY™ PAR Reflectors

Not Shown Actual Size

## PAR16/PAR20/PAR30/PAR38

### Frosted Halogen Lamps

#### S O F T - R A Y

Introducing - Soft Ray, a new concept in halogen lighting. Our new line of frosted MR16 and PAR lamps offer a simple, cost effective solution to problems normally associated with standard halogen reflectors.

It is known that many users of traditional MR16 & PAR lamps object to the "headlamp look" or glare appearance of these lamps. Soft Ray lamps solve these problems and more!

- Glare Free
- Does not create hot spots
- Eliminates shadows & striations
- Produces a smooth and even beam pattern



PAR16



PAR20



PAR30 Short Neck



PAR30 Long Neck



PAR38

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
60	PAR16	Med.	S4108	60PAR16/FL/FROST	Flood 38°	120V	2500	525	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S4109	75PAR16/FL/FROST	Flood 38°	120V	2500	725	CC-8	3 3/16"	Box	15
50	PAR20	Med.	S4100	50PAR20/NFL/FROST	Flood 38°	120V	2500	450	CC-8	3 3/8"	Box	15
50	PAR20	Med.	S4200	50PAR20/NFL/FROST	Flood 38°	130V	2500	450	CC-8	3 3/8"	Box	15
50	PAR30	Med.	S4101	50PAR30/FL/FROST	Flood 38°	120V	2500	520	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S4201	50PAR30/FL/FROST	Flood 38°	130V	2500	520	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S4102	75PAR30/FL/FROST	Flood 38°	120V	2500	900	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S4202	75PAR30/FL/FROST	Flood 38°	130V	2500	900	CC-8	5 5/16"	Box	15
50	PAR30/LN	Med.	S4103	50PAR30/LN/FL/FROST	Flood 38°	120V	2500	520	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S4203	50PAR30/LN/FL/FROST	Flood 38°	130V	2500	520	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S4104	75PAR30/LN/FL/FROST	Flood 38°	120V	2500	900	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S4204	75PAR30/LN/FL/FROST	Flood 38°	130V	2500	900	CC-8	4 1/2"	Box	15
45	PAR38	Med. Skt.	S4105	45PAR38/FL/FROST	Flood 38°	120V	2500	450	CC-8	5 5/16"	Box	15
45	PAR38	Med. Skt.	S4205	45PAR38/FL/FROST	Flood 38°	130V	2500	450	CC-8	5 5/16"	Box	15
60	PAR38	Med. Skt.	S4106	60PAR38/FL/FROST	Flood 38°	120V	2500	600	CC-8	5 5/16"	Box	15
60	PAR38	Med. Skt.	S4206	60PAR38/FL/FROST	Flood 38°	130V	2500	600	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4107	90PAR38/FL/FROST	Flood 38°	120V	2500	1150	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4207	90PAR38/FL/FROST	Flood 38°	130V	2500	1150	CC-8	5 5/16"	Box	15

## PAR16/PAR20/PAR30

*Whiter light, brighter colors, precise beam control.*

Not Shown Actual Size



PAR16

PAR20

PAR30

### SATCO PAR HALOGEN LAMPS QUALITY • VALUE • PERFORMANCE

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated		Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
							Hours	CBCP					
45	PAR16	Med.	S2200	45PAR16/HAL/NFL	NFL 30°	120V	2500	1200	420	CC-8	3 3/16"	Box	15
45	PAR16	Med.	S2300	45PAR16/HAL/NFL	NFL 30°	130V	2500	1200	420	CC-8	3 3/16"	Box	15
60	PAR16	Med.	S2201	60PAR16/HAL/NFL	NFL 30°	120V	2500	1400	600	CC-8	3 3/16"	Box	15
60	PAR16	Med.	S2301	60PAR16/HAL/NFL	NFL 30°	130V	2500	1400	600	CC-8	3 3/16"	Box	15
60	PAR16	Med.	S2202	60PAR16/HAL/NSP	NSP 10°	120V	2500	4700	550	CC-8	3 3/16"	Box	15
60	PAR16	Med.	S2302	60PAR16/HAL/NSP	NSP 10°	130V	2500	4700	550	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S2203	75PAR16/HAL/NFL	NFL 30°	120V	2500	1800	850	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S2303	75PAR16/HAL/NFL	NFL 30°	130V	2500	1800	850	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S2204	75PAR16/HAL/NSP	NSP 10°	120V	2500	7000	850	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S2304	75PAR16/HAL/NSP	NSP 10°	130V	2500	7000	850	CC-8	3 3/16"	Box	15
50	PAR20	Med.	S2205	50PAR20/HAL/NFL	NFL 34°	120V	2500	1300	495	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S2305	50PAR20/HAL/NFL	NFL 34°	130V	2500	1300	495	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S2206	50PAR20/HAL/NSP	NSP 10°	120V	2500	4700	495	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S2306	50PAR20/HAL/NSP	NSP 10°	130V	2500	4700	495	CC-8	3 1/4"	Box	15
50	PAR30	Med.	S2207	50PAR30/HAL/NFL	NFL 34°	120V	2500	1750	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2307	50PAR30/HAL/NFL	NFL 34°	130V	2500	1750	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2208	50PAR30/HAL/WFL	WFL 50°	120V	2500	460	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2308	50PAR30/HAL/WFL	WFL 50°	130V	2500	460	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2209	50PAR30/HAL/NSP	NSP 9°	120V	2500	7600	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2309	50PAR30/HAL/NSP	NSP 9°	130V	2500	7600	56+0	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2210	75PAR30/HAL/NFL	NFL 34°	120V	2500	3100	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2310	75PAR30/HAL/NFL	NFL 34°	130V	2500	3100	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2211	75PAR30/HAL/WFL	WFL 50°	120V	2500	770	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2311	75PAR30/HAL/WFL	WFL 50°	130V	2500	770	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2212	75PAR30/HAL/NSP	NSP 9°	120V	2500	13000	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2312	75PAR30/HAL/NSP	NSP 9°	130V	2500	13000	945	CC-8	3 5/8"	Box	15

Not Shown Actual Size



PAR38

PAR30LN

### SATCO PAR HALOGEN LAMPS

QUALITY • VALUE • PERFORMANCE

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Avg. Rated				Filament	M.O.L.	Pack Type	Mst. Ctn.
						Volts	Hours	CBCP*	Lumens				
50	PAR30/LN	Med.	S2213	50PAR30/HAL/NFL	NFL 34°	120V	2500	1750	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2313	50PAR30/HAL/NFL	NFL 34°	130V	2500	1750	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2214	50PAR30/HAL/WFL	WFL 50°	120V	2500	460	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2314	50PAR30/HAL/WFL	WFL 50°	130V	2500	460	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2215	50PAR30/HAL/NSP	NSP 9°	120V	2500	7600	550	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S2315	50PAR30/HAL/NSP	NSP 9°	130V	2500	7600	550	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2216	75PAR30/HAL/NFL	NFL 34°	120V	2500	3100	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2316	75PAR30/HAL/NFL	NFL 34°	130V	2500	3100	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2217	75PAR30/HAL/WFL	WFL 50°	120V	2500	770	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2317	75PAR30/HAL/WFL	WFL 50°	130V	2500	770	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2218	75PAR30/HAL/NSP	NSP 9°	120V	2500	13000	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S2318	75PAR30/HAL/NSP	NSP 9°	130V	2500	13000	945	CC-8	4 1/2"	Box	15
45	PAR38	Med.	S2219	45PAR38/HAL/FL	FL 30°	120V	2500	1380	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	S2319	45PAR38/HAL/FL	FL 30°	130V	2500	1380	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	S2220	45PAR38/HAL/NSP	NSP 9°	120V	2500	5000	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	S2320	45PAR38/HAL/NSP	NSP 9°	130V	2500	5000	465	CC-8	5 5/16"	Box	15
75	PAR38	Med.	S2221	75PAR38/HAL/FL	FL 30°	120V	2500	3200	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	S2321	75PAR38/HAL/FL	FL 30°	130V	2500	3200	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	S2222	75PAR38/HAL/NSP	NSP 9°	120V	2500	16000	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	S2322	75PAR38/HAL/NSP	NSP 9°	130V	2500	16000	960	CC-8	5 5/16"	Box	15
90	PAR38	Med.	S2223	90PAR38/HAL/FL	FL 30°	120V	2500	3800	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	S2323	90PAR38/HAL/FL	FL 30°	130V	2500	3800	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	S2224	90PAR38/HAL/NSP	NSP 9°	120V	2500	14000	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	S2324	90PAR38/HAL/NSP	NSP 9°	130V	2500	14000	1260	CC-8	5 5/16"	Box	15
120	PAR38	Med.	S2225	120PAR38/HAL/FL	FL 30°	120V	2500	4700	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	S2325	120PAR38/HAL/FL	FL 30°	130V	2500	4700	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	S2226	120PAR38/HAL/NSP	NSP 9°	120V	2500	22000	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	S2326	120PAR38/HAL/NSP	NSP 9°	130V	2500	22000	1600	CC-8	5 5/16"	Box	15

reflectors

# Halogen

## PAR14/PAR16/PAR20

Whiter light, brighter colors, precise beam control.



PAR14

PAR16

PAR20

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Avg. Rated		CBCP	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
						Volts	Hours						
35	PAR14	Med.	S4658	35PAR14/CAP/WFL	WFL 50°	120V	2000	85	300	CC-8	2 7/16"	Box	6
60	PAR16	Med.	S4900	60PAR16/CAP/NFL	NFL 30°	120V	2000	1300	650	CC-8	2 7/8"	Box	15
60	PAR16	Med.	S4901	60PAR16/CAP/NFL	NFL 30°	130V	2000	1300	650	CC-8	2 7/8"	Box	15
60	PAR16	Med.	S4902	60PAR16/CAP/NSP	NSP 10°	120V	2000	5000	650	CC-8	2 7/8"	Box	15
60	PAR16	Med.	S4903	60PAR16/CAP/NSP	NSP 10°	130V	2000	5000	650	CC-8	2 7/8"	Box	15
75	PAR16	Med.	S4904	75PAR16/CAP/NFL	NFL 30°	120V	2000	1900	900	CC-8	2 7/8"	Box	15
75	PAR16	Med.	S4905	75PAR16/CAP/NFL	NFL 30°	130V	2000	1900	900	CC-8	2 7/8"	Box	15
75	PAR16	Med.	S4906	75PAR16/CAP/NSP	NSP 10°	120V	2000	7500	900	CC-8	2 7/8"	Box	15
75	PAR16	Med.	S4907	75PAR16/CAP/NSP	NSP 10°	130V	2000	7500	900	CC-8	2 7/8"	Box	15
35	PAR20	Med.	S4908	35PAR20/CAP/NFL	NFL 30°	120V	2500	800	360	CC-8	3 1/4"	Box	15
35	PAR20	Med.	S4663	35PAR20/CAP/NFL	NFL 30°	130V	2500	800	360	CC-8	3 1/4"	Box	15
35	PAR20	Med.	S4909	35PAR20/CAP/NSP	NSP 10°	120V	2500	3000	360	CC-8	3 1/4"	Box	15
35	PAR20	Med.	S4661	35PAR20/CAP/NSP	NSP 10°	130V	2500	3000	360	CC-8	3 1/4"	Box	15
35	PAR20	Med.	S4910	35PAR20/CAP/WFL	WFL 40°	120V	2500	500	360	CC-8	3 1/8"	Box	15
35	PAR20	Med.	S4665	35PAR20/CAP/WFL	WFL 40°	120V	2500	500	360	CC-8	3 1/8"	Box	15
50	PAR20	Med.	S4911	50PAR20/CAP/NFL	NFL 30°	120V	2500	1400	550	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S4912	50PAR20/CAP/NFL	NFL 30°	130V	2500	1400	550	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S4913	50PAR20/CAP/NSP	NSP 10°	120V	2500	6200	550	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S4914	50PAR20/CAP/NSP	NSP 10°	130V	2500	6200	550	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S4666	50PAR20/CAP/WFL	WFL 40°	120V	2500	900	550	CC-8	3 1/8"	Box	15

# Halogen **PAR30** Short & Long Neck

*Whiter light, brighter colors, precise beam control.*

Not Shown Actual Size



**PAR30 Short Neck**



**PAR30 Long Neck**

reflector

## SHORT NECK

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP*	Lumens	Filament	M.O.L.	Pack Type	Mst. Ctn.
50	PAR30	Med.	<b>S4915</b>	50PAR30/CAP/FL	FL 40°	120V	2500	1300	600	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4916</b>	50PAR30/CAP/FL	FL 40°	130V	2500	1300	600	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4917</b>	50PAR30/CAP/NFL	NFL 25°	120V	2500	2300	660	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4918</b>	50PAR30/CAP/NFL	NFL 25°	130V	2500	2300	660	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4919</b>	50PAR30/CAP/NSP	NSP 9°	120V	2500	8800	660	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4920</b>	50PAR30/CAP/NSP	NSP 9°	130V	2500	8800	660	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4921</b>	75PAR30/CAP/FL	FL 40°	120V	2500	2000	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4922</b>	75PAR30/CAP/FL	FL 40°	130V	2500	2000	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4923</b>	75PAR30/CAP/NFL	NFL 25°	120V	2500	4000	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4924</b>	75PAR30/CAP/NFL	NFL 25°	130V	2500	4000	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4925</b>	75PAR30/CAP/NSP	NSP 9°	120V	2500	15400	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4926</b>	75PAR30/CAP/NSP	NSP 9°	130V	2500	15400	1130	CC-8	3 5/8"	Box	15

## LONG NECK

35	PAR30/LN	Med.	<b>S2654</b>	35PAR30LN/CAP/WFL	WFL 50°	120V	2500	450	450	CC-8	4 5/8"	Box	15
35	PAR30/LN	Med.	<b>S2655</b>	35PAR30LN/CAP/NSP	NSP 9°	120V	2500	5700	450	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4927</b>	50PAR30LN/CAP/WFL	WFL 50°	120V	2500	660	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4928</b>	50PAR30LN/CAP/WFL	WFL 50°	130V	2500	660	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4929</b>	50PAR30LN/CAP/NFL	NFL 25°	120V	2500	2300	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4930</b>	50PAR30LN/CAP/NFL	NFL 25°	130V	2500	2300	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4931</b>	50PAR30LN/CAP/NSP	NSP 9°	120V	2500	8800	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4932</b>	50PAR30LN/CAP/NSP	NSP 9°	130V	2500	8800	660	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4933</b>	75PAR30LN/CAP/WFL	WFL 50°	120V	2500	1100	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4934</b>	75PAR30LN/CAP/WFL	WFL 50°	130V	2500	1100	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4935</b>	75PAR30LN/CAP/NFL	NFL 25°	120V	2500	4000	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4936</b>	75PAR30LN/CAP/NFL	NFL 25°	130V	2500	4000	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4937</b>	75PAR30LN/CAP/NSP	NSP 9°	120V	2500	15400	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4938</b>	75PAR30LN/CAP/NSP	NSP 9°	130V	2500	15400	1130	CC-8	4 5/8"	Box	15



# Reflectors **PAR38**

Not Shown Actual Size

Whiter light,  
brighter colors,  
precise beam  
control.



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated		CBCP*	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
							Hours							
45	PAR38	Med. Skt.	<b>S4939</b>	45PAR/CAP/FL	FL 30°	120V	2500	1500	560	CC-8	5 5/16"	Box	15	
45	PAR38	Med. Skt.	<b>S4940</b>	45PAR/CAP/FL	FL 30°	130V	2500	1500	560	CC-8	5 5/16"	Box	15	
45	PAR38	Med. Skt.	<b>S4941</b>	45PAR/CAP/NSP	NSP 9°	120V	2500	10000	560	CC-8	5 5/16"	Box	15	
45	PAR38	Med. Skt.	<b>S4942</b>	45PAR/CAP/NSP	NSP 9°	130V	2500	10000	560	CC-8	5 5/16"	Box	15	
45	PAR38	Med. Skt.	<b>S4630</b>	45PAR/CAP/WFL	WFL 50°	130V	2500	700	560	CC-8	5 5/16"	Box	15	
60	PAR38	Med. Skt.	<b>S4943</b>	60PAR/CAP/FL	FL 30°	120V	3000	2500	850	CC-8	5 5/16"	Box	15	
60	PAR38	Med. Skt.	<b>S4944</b>	60PAR/CAP/FL	FL 30°	130V	3000	2500	850	CC-8	5 5/16"	Box	15	
60	PAR38	Med. Skt.	<b>S4945</b>	60PAR/CAP/NSP	NSP 9°	120V	3000	16000	850	CC-8	5 5/16"	Box	15	
60	PAR38	Med. Skt.	<b>S4946</b>	60PAR/CAP/NSP	NSP 9°	130V	3000	16000	850	CC-8	5 5/16"	Box	15	
75	PAR38	Med. Skt.	<b>S4964</b>	75PAR/CAP/FL	FL 30°	120V	2500	3150	1060	CC-8	5 5/16"	Box	15	
75	PAR38	Med. Skt.	<b>S4965</b>	75PAR/CAP/FL	FL 30°	130V	2500	3150	1060	CC-8	5 5/16"	Box	15	
75	PAR38	Med. Skt.	<b>S4966</b>	75PAR/CAP/NSP	NSP 9°	120V	2500	19200	1060	CC-8	5 5/16"	Box	15	
75	PAR38	Med. Skt.	<b>S4967</b>	75PAR/CAP/NSP	NSP 9°	130V	2500	19200	1060	CC-8	5 5/16"	Box	15	
75	PAR38	Med. Skt.	<b>S4631</b>	75PAR/CAP/WFL	WFL 50°	130V	2500	1300	1060	CC-8	5 5/16"	Box	15	
90	PAR38	Med. Skt.	<b>S4968</b>	90PAR/CAP/FL	FL 30°	120V	2500	3500	1310	CC-8	5 5/16"	Box	15	
90	PAR38	Med. Skt.	<b>S4969</b>	90PAR/CAP/FL	FL 30°	130V	2500	3500	1310	CC-8	5 5/16"	Box	15	
90	PAR38	Med. Skt.	<b>S4970</b>	90PAR/CAP/NSP	NSP 9°	120V	2500	19000	1310	CC-8	5 5/16"	Box	15	
90	PAR38	Med. Skt.	<b>S4971</b>	90PAR/CAP/NSP	NSP 9°	130V	2500	19000	1310	CC-8	5 5/16"	Box	15	
90	PAR38	Med. Skt.	<b>S4950</b>	90PAR/CAP/WSP	WSP 12°	120V	2500	14300	1310	CC-8	5 5/16"	Box	15	
90	PAR38	Med. Skt.	<b>S4951</b>	90PAR/CAP/WSP	WSP 12°	130V	2500	14300	1310	CC-8	5 5/16"	Box	15	
90	PAR38	Med. Skt.	<b>S4632</b>	90PAR/CAP/NFL	NFL 25°	130V	2500	4700	1310	CC-8	5 5/16"	Box	15	
90	PAR38	Med. Skt.	<b>S4633</b>	90PAR/CAP/WFL	WFL 50°	130V	2500	1600	1310	CC-8	5 5/16"	Box	15	
120	PAR38	Med. Skt.	<b>S4972</b>	120PAR/CAP/FL	FL 30°	120V	3000	4600	1800	CC-8	5 5/16"	Box	15	
120	PAR38	Med. Skt.	<b>S4973</b>	120PAR/CAP/FL	FL 30°	130V	3000	4600	1800	CC-8	5 5/16"	Box	15	
120	PAR38	Med. Skt.	<b>S4974</b>	120PAR/CAP/SP	SP 10°	120V	3000	22500	1800	CC-8	5 5/16"	Box	15	
120	PAR38	Med. Skt.	<b>S4975</b>	120PAR/CAP/SP	SP 10°	130V	3000	22500	1800	CC-8	5 5/16"	Box	15	
120	PAR38	Med. Skt.	<b>S4634</b>	120PAR/CAP/WFL	WFL 50°	130V	3000	2000	1800	CC-8	5 5/16"	Box	15	
250	PAR38	Med. Skt.	<b>S4947</b>	250PAR/CAP/FL	FL 30°	120V	4500	4500	3600	CC-8	5 5/16"	Box	6	
250	PAR38	Med. Skt.	<b>S4948</b>	250PAR/CAP/SP	SP 10°	120V	4500	46500	3600	CC-8	5 5/16"	Box	6	

reflectors

# Lights

1500 Hours/120V

decorative incandescent lamps

**G8 1" Round**

**Glossy White**  
Candelabra Base  
(120 Volt)  
**S3864** 10 Watt  
Packing:  
Individually Boxed  
1000/Master, 25/Inner



**G12 1 1/2" Round**

**Clear**  
Candelabra Base  
(120 Volt)  
**S3844** 10 Watt  
**S3845** 15 Watt  
**S3846** 25 Watt  
**S3847** 40 Watt  
Packing:  
Individually Boxed  
500/Master, 25/Inner



**G12 1 1/2" Pear**

**Satin White**  
Candelabra Base  
(120 Volt)  
**S3879** 15 Watt  
**S3863** 25 Watt  
Packing:  
Individually Boxed  
500/Master, 25/Inner



**G12 1 1/2" Round**

**Satin White**  
Candelabra Base  
**S3830** 10 Watt  
(120 Volt)  
Packing:  
Individually Boxed  
500/Master, 25/Inner



Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
10	G8	Cand.	<b>S3864</b>	10G8/W	White	120V	1500	50	C7A	1 7/8"	Box	1000/25
10	G12 1/2	Cand.	<b>S3844</b>	10G12 1/2	Clear	120V	1500	60	C7A	2 3/8"	Box	500/25
10	G12 1/2	Cand.	<b>S3830</b>	10G12 1/2/W	White	120V	1500	50	C7A	2 3/8"	Box	500/25
15	G12 1/2	Cand.	<b>S3845</b>	15G12 1/2	Clear	120V	1500	100	C7A	2 3/8"	Box	500/25
25	G12 1/2	Cand.	<b>S3846</b>	25G12 1/2	Clear	120V	1500	180	C7A	2 3/8"	Box	500/25
40	G12 1/2	Cand.	<b>S3847</b>	40G12 1/2	Clear	120V	1500	370	C7A	2 3/8"	Box	500/25
15	G12 1/2	Cand.	<b>S3879</b>	15G12 1/2/W	White	120V	1500	100	C7A	2 3/8"	Box	500/25
25	G12 1/2	Cand.	<b>S3863</b>	25G12 1/2/W	White	120V	1500	180	C7A	2 3/8"	Box	500/25

Globe Lights

1500 Hours



**S3834** 10 Watt Blue



**S3835** 10 Watt Green



**S3836** 10 Watt Amber



**S3837** 10 Watt Pink



**S3833** 10 Watt Red

**G12 1 1/2" Round  
Transparent Colors**

Candelabra Base (120 Volt)

Packing: Individually Boxed  
500/Master, 25/Inner



Shown Actual Size

**G16 1/2 2 1/8"**

**Silver Crown**

Candelabra Base  
(120 Volt)

**S3244** 25 Watt

**S3245** 40 Watt

**S3246** 60 Watt

Packing: Individually Boxed  
500/Master, 25/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
10	G12 1/2	Cand.	<b>S3833</b>	10G12 1/2/R	Red	120V	1500	n/a	C7A	2 3/8"	Box	500/25
10	G12 1/2	Cand.	<b>S3834</b>	10G12 1/2/B	Blue	120V	1500	n/a	C7A	2 3/8"	Box	500/25
10	G12 1/2	Cand.	<b>S3835</b>	10G12 1/2/G	Green	120V	1500	n/a	C7A	2 3/8"	Box	500/25
10	G12 1/2	Cand.	<b>S3836</b>	10G12 1/2/A	Amber	120V	1500	n/a	C7A	2 3/8"	Box	500/25
10	G12 1/2	Cand.	<b>S3837</b>	10G12 1/2/PK	Pink	120V	1500	n/a	C7A	2 3/8"	Box	500/25
25	G16 1/2	Cand.	<b>S3244</b>	25G16 1/2/SL	Silver	120V	1500	232	CC-2V	3"	Box	500/25
40	G16 1/2	Cand.	<b>S3245</b>	40G16 1/2/SL	Silver	120V	1500	384	CC-2V	3"	Box	500/25
60	G16 1/2	Cand.	<b>S3246</b>	60G16 1/2/SL	Silver	120V	1500	672	CC-2V	3"	Box	500/25

decorative incandescent lamps

# G16 1/2 Brass Base



## Globe Lights 2 1/8"

1500 Hours



Satin White



Clear



Glossy White

Candelabra Base  
(120 Volt)

- S3824** 15 Watt
- S3825** 25 Watt
- S3826** 40 Watt
- S3832** 60 Watt

Packing: Individually Boxed  
500/Master, 25/Inner

Candelabra Base  
(120 Volt)

- S3821** 15 Watt
- S3822** 25 Watt
- S3823** 40 Watt
- S3831** 60 Watt

Packing: Individually Boxed  
500/Master, 25/Inner

Candelabra Base  
(120 Volt)

- S3236** 15 Watt
- S3260** 25 Watt
- S3261** 40 Watt
- S3271** 60 Watt

Packing: Individually Boxed  
500/Master, 25/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
15	G16 1/2	Cand.	<b>S3821</b>	15G16 1/2	Clear	120V	1500	114	C7A	3"	Box	500/25
15	G16 1/2	Cand.	<b>S3824</b>	15G16 1/2W	Sat. White	120V	1500	94	C7A	3"	Box	500/25
15	G16 1/2	Cand.	<b>S3236</b>	15G16 1/2W	Gloss. White	120V	1500	94	C7A	3"	Box	500/25
25	G16 1/2	Cand.	<b>S3822</b>	25G16 1/2	Clear	120V	1500	232	C7A	3"	Box	500/25
25	G16 1/2	Cand.	<b>S3825</b>	25G16 1/2W	Sat. White	120V	1500	202	C7A	3"	Box	500/25
25	G16 1/2	Cand.	<b>S3260</b>	25G16 1/2W	Gloss White	120V	1500	202	C7A	3"	Box	500/25
40	G16 1/2	Cand.	<b>S3823</b>	40G16 1/2	Clear	120V	1500	384	CC-2V	3"	Box	500/25
40	G16 1/2	Cand.	<b>S3826</b>	40G16 1/2W	Sat. White	120V	1500	348	CC-2V	3"	Box	500/25
40	G16 1/2	Cand.	<b>S3261</b>	40G16 1/2W	Gloss White	120V	1500	348	CC-2V	3"	Box	500/25
60	G16 1/2	Cand.	<b>S3831</b>	60G16 1/2	Clear	120V	1500	672	CC-2V	3"	Box	500/25
60	G16 1/2	Cand.	<b>S3832</b>	60G16 1/2W	Sat. White	120V	1500	630	CC-2V	3"	Box	500/25
60	G16 1/2	Cand.	<b>S3271</b>	60G16 1/2W	Gloss. White	120V	1500	630	CC-2V	3"	Box	500/25

decorative incandescent lamps

*2500 Hours / 130 Volt*

**Globe Lights 2 1/8"**



*Clear*



*Satin White*

*Candelabra Base  
(130 Volt)*

- A3921** 15 Watt
- A3922** 25 Watt
- A3923** 40 Watt
- A3931** 60 Watt

*Packing: Individually Boxed  
500/Master, 25/Inner*

*Candelabra Base  
(130 Volt)*

- A3924** 15 Watt
- A3925** 25 Watt
- A3926** 40 Watt
- A3932** 60 Watt

*Packing: Individually Boxed  
500/Master, 25/Inner*

*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	G16 1/2	Cand.	<b>A3921</b>	15G16 1/2	Clear	130V	2500	98	C7A	3"	Box	500/25
15	G16 1/2	Cand.	<b>A3924</b>	15G16 1/2W	White	130V	2500	83	C7A	3"	Box	500/25
25	G16 1/2	Cand.	<b>A3922</b>	25G16 1/2	Clear	130V	2500	186	C7A	3"	Box	500/25
25	G16 1/2	Cand.	<b>A3925</b>	25G16 1/2W	White	130V	2500	162	C7A	3"	Box	500/25
40	G16 1/2	Cand.	<b>A3923</b>	40G16 1/2	Clear	130V	2500	360	CC-2V	3"	Box	500/25
40	G16 1/2	Cand.	<b>A3926</b>	40G16 1/2W	White	130V	2500	325	CC-2V	3"	Box	500/25
60	G16 1/2	Cand.	<b>A3931</b>	60G16 1/2	Clear	130V	2500	642	CC-2V	3"	Box	500/25
60	G16 1/2	Cand.	<b>A3932</b>	60G16 1/2W	White	130V	2500	564	CC-2V	3"	Box	500/25

decorative incandescent lamps

# Globe Lights

1000 Hours/130 Volts



**G14**

**White**  
Euro Base  
(130 Volt)  
**S3398** 40 Watt  
Packing:  
Individually Boxed  
500/Master, 25/Inner



**G14**

**Clear**  
Euro Base  
(130 Volt)  
**S3397** 40 Watt  
Packing:  
Individually Boxed  
500/Master, 25/Inner



**G17**

**Medicine  
Cabinet  
Bulb  
Frosted**  
E27 Base  
(130 Volt)  
**S3967** 40 Watt  
Packing:  
Individually Boxed  
500/Master, 25/Inner



**G17**

**Medicine  
Cabinet  
Bulb  
White**  
E27 Base  
(130 Volt)  
**S3968** 40 Watt  
Packing:  
Individually Boxed  
500/Master, 25/Inner

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
40	G14	E14/Euro.	<b>S3397</b>	40G14	Clear	130V	1000	368	CC9	31/8	Box	500/25
40	G14	E14/Euro	<b>S3398</b>	40G14/W	White	130V	1000	320	CC9	31/8	Box	500/25
40	G17	E27/Med.	<b>S3967</b>	40G17/IF	Frost	130V	1000	348	CC9	31/8	Box	500/25
40	G17	E27/Med.	<b>S3968</b>	40G17/W	White	130V	1000	320	CC9	31/8	Box	500/25

decorative incandescent lamps

**1500 Hours / 120 Volt**

**Globe Lights**

*Not Shown Actual Size*

**G16 1/2 2 1/8"**

**Glossy White**  
Medium Base  
(120 Volt)

- S3841** 25 Watt
- S3842** 40 Watt
- S3843** 60 Watt

**Packing:**  
Individually Boxed  
500/Master, 25/Inner



**G16 1/2 2 1/8"**  
**Clear**

Medium Base  
(120 Volt)

- S3838** 25 Watt
- S3839** 40 Watt
- S3840** 60 Watt

**Packing:**  
Individually Boxed  
500/Master, 25/Inner



**G18 1/2 2 3/8"**

**Glossy White**  
Medium Base  
(120 Volt)

- S3827** 25 Watt
- S3828** 40 Watt
- S3829** 60 Watt

**Packing:**  
Individually Boxed  
250/Master, 25/Inner



**G18 1/2 2 3/8"**  
**Clear**

Medium Base  
(120 Volt)

- S3887** 25 Watt
- S3888** 40 Watt
- S3889** 60 Watt

**Packing:**  
Individually Boxed  
250/Master, 25/Inner



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	G16 1/2	Med.	<b>S3838</b>	25G16 1/2	Clear	120V	1500	210	CC-2V	3 1/4"	Box	500/25
25	G16 1/2	Med.	<b>S3841</b>	25G16 1/2W	White	120V	1500	160	CC-2V	3 1/4"	Box	500/25
40	G16 1/2	Med.	<b>S3839</b>	40G16 1/2	Clear	120V	1500	370	CC-2V	3 1/4"	Box	500/25
40	G16 1/2	Med.	<b>S3842</b>	40G16 1/2W	White	120V	1500	320	CC-2V	3 1/4"	Box	500/25
60	G16 1/2	Med.	<b>S3840</b>	60G16 1/2	Clear	120V	1500	650	CC-2V	3 1/4"	Box	500/25
60	G16 1/2	Med.	<b>S3843</b>	60G16 1/2W	White	120V	1500	550	CC-2V	3 1/4"	Box	500/25
25	G18 1/2	Med.	<b>S3887</b>	25G18 1/2	Clear	120V	1500	158	C-9	3 1/2"	Box	250/25
25	G18 1/2	Med.	<b>S3827</b>	25G18 1/2W	White	120V	1500	120	C-9	3 1/2"	Box	250/25
40	G18 1/2	Med.	<b>S3888</b>	40G18 1/2	Clear	120V	1500	368	C-9	3 1/2"	Box	250/25
40	G18 1/2	Med.	<b>S3828</b>	40G18 1/2W	White	120V	1500	280	C-9	3 1/2"	Box	250/25
60	G18 1/2	Med.	<b>S3889</b>	60G18 1/2	Clear	120V	1500	610	C-9	3 1/2"	Box	250/25
60	G18 1/2	Med.	<b>S3829</b>	60G18 1/2W	White	120V	1500	530	C-9	3 1/2"	Box	250/25

decorative incandescent lamps

**G25 Brass Base**

**SATCO®**

# Globe Lights 3 1/8" 120V

**2500 Hours**

**Clear**

Medium Base  
(120 Volt)

- S3447** 25 Watt
- S3448** 40 Watt
- S3449** 60 Watt
- S3450** 100 Watt

Packing:  
Individually Boxed  
72/Master, 6/Inner



*Shown Actual Size*



**White**

Medium Base  
(120 Volt)

- S3440** 25 Watt
- S3441** 40 Watt
- S3442** 60 Watt
- S3443** 100 Watt

Packing:  
Individually Boxed  
72/Master, 6/Inner



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	G25	Med.	<b>S3447</b>	25G25	Clear	120V	2500	212	CC-9	4 3/8"	Box	72/6
25	G25	Med.	<b>S3440</b>	25G25/W	White	120V	2500	187	CC-9	4 3/8"	Box	72/6
40	G25	Med.	<b>S3448</b>	40G25	Clear	120V	2500	384	CC-9	4 3/8"	Box	72/6
40	G25	Med.	<b>S3441</b>	40G25/W	White	120V	2500	340	CC-9	4 3/8"	Box	72/6
60	G25	Med.	<b>S3449</b>	60G25	Clear	120V	2500	650	CC-9	4 3/8"	Box	72/6
60	G25	Med.	<b>S3442</b>	60G25/W	White	120V	2500	575	CC-9	4 3/8"	Box	72/6
100	G25	Med.	<b>S3450</b>	100G25	Clear	120V	2500	1000	CC-9	4 3/8"	Box	72/6
100	G25	Med.	<b>S3443</b>	100G25/W	White	120V	2500	920	CC-9	4 3/8"	Box	72/6

decorative incandescent lamps



*3000 Hours*

# Globe Lights 3 1/8" 130V




*Shown Actual Size*



**Clear**  
 Medium Base  
 (130 Volt)  
**A3647** 25 Watt  
**A3648** 40 Watt  
**A3649** 60 Watt  
**A3650** 100 Watt  
 Packing:  
 Individually Boxed  
 72/Master, 6/Inner



**White**  
 Medium Base  
 (130 Volt)  
**A3640** 25 Watt  
**A3641** 40 Watt  
**A3642** 60 Watt  
**A3643** 100 Watt  
 Packing:  
 Individually Boxed  
 72/Master, 6/Inner



decorative incandescent lamps

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./Inner Pack
25	G25	Med.	<b>A3647</b>	25G25	Clear	130V	3000	193	CC-9	4 3/8"	Box	72/6
25	G25	Med.	<b>A3640</b>	25G25/W	White	130V	3000	167	CC-9	4 3/8"	Box	72/6
40	G25	Med.	<b>A3648</b>	40G25	Clear	130V	3000	360	CC-9	4 3/8"	Box	72/6
40	G25	Med.	<b>A3641</b>	40G25/W	White	130V	3000	320	CC-9	4 3/8"	Box	72/6
60	G25	Med.	<b>A3649</b>	60G25	Clear	130V	3000	642	CC-9	4 3/8"	Box	72/6
60	G25	Med.	<b>A3642</b>	60G25/W	White	130V	3000	564	CC-9	4 3/8"	Box	72/6
100	G25	Med.	<b>A3650</b>	100G25	Clear	130V	3000	1000	CC-9	4 3/8"	Box	72/6
100	G25	Med.	<b>A3643</b>	100G25/W	White	130V	3000	920	CC-9	4 3/8"	Box	72/6

**G25** Brass Base



# Globe Lights 3 1/8" 120V

2500 Hours

## 3 Pack

### Clear

Medium Base  
(120 Volt)

**S4048** 40 Watt

**S4049** 60 Watt

Packing: 3/Box  
40 3-Packs /Master  
Sold Per Pack



### White

Medium Base  
(120 Volt)

**S4041** 40 Watt

**S4042** 60 Watt

Packing: 3/Box  
40 3-Packs /Master  
Sold Per Pack



Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
40	G25	Med.	<b>S4048</b>	40G25/3PK	Clear	120V	2500	384	CC-9	4 3/8"	Box/3	40
40	G25	Med.	<b>S4041</b>	40G25/W/3PK	White	120V	2500	340	CC-9	4 3/8"	Box/3	40
60	G25	Med.	<b>S4049</b>	60G25/3PK	Clear	120V	2500	650	CC-9	4 3/8"	Box/3	40
60	G25	Med.	<b>S4042</b>	60G25/W/3PK	White	120V	2500	575	CC-9	4 3/8"	Box/3	40

decorative incandescent lamps

**ALLURA®**

*Brass Base* **G25**

*3000 Hours*

# Globe Lights 3 1/8" 130V



**Clear**  
Medium Base  
(130 Volt)  
**A4148** 40 Watt  
**A4149** 60 Watt  
Packing: 3/Box  
40 3-Packs /Master  
**Sold Per Pack**

*Shown Actual Size*



**3 Pack**



**White**  
Medium Base  
(130 Volt)  
**A4141** 40 Watt  
**A4142** 60 Watt  
Packing: 3/Box  
40 3-Packs /Master  
**Sold Per Pack**

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
40	G25	Med.	<b>A4148</b>	40G25/3PK	Clear	130V	3000	360	CC-9	4 3/8"	Box/3	40
40	G25	Med.	<b>A4141</b>	40G25/W/3PK	White	130V	3000	320	CC-9	4 3/8"	Box/3	40
60	G25	Med.	<b>A4149</b>	60G25/3PK	Clear	130V	3000	642	CC-9	4 3/8"	Box/3	40
60	G25	Med.	<b>A4142</b>	60G25/W/3PK	White	130V	3000	564	CC-9	4 3/8"	Box/3	40

decorative incandescent lamps

# G25 & G30 Brass Base



## Globe Lights

120V

Not Shown Actual Size

### G25 3 1/8"

Silver Crown

Medium Base

1500 Hrs. Average Life  
(120 Volt)

**S3860** 25 Watt

**S3861** 40 Watt

**S3862** 60 Watt

Packing: Individually Boxed  
72/Master, 6/Inner



### G30 3 3/4"

Medium Base

2500 Hrs. Average Life  
(120 Volt)

Clear

**S3651** 25 Watt

**S3652** 40 Watt

**S3670** 60 Watt

White

**S3653** 25 Watt

**S3671** 40 Watt

**S3672** 60 Watt

Packing:  
Individually Boxed  
72/Master, 6/Inner



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
25	G25	Med.	<b>S3860</b>	25G25/SL	Silver	120V	1500	170	CC-9	4 3/8"	Box	72/6
40	G25	Med.	<b>S3861</b>	40G25/SL	Silver	120V	1500	280	CC-9	4 3/8"	Box	72/6
60	G25	Med.	<b>S3862</b>	60G25/SL	Silver	120V	1500	512	CC-9	4 3/8"	Box	72/6
25	G30	Med.	<b>S3651</b>	25G30	Clear	120V	2500	212	CC-9	5 1/8"	Box	72/6
25	G30	Med.	<b>S3653</b>	25G30W	White	120V	2500	187	CC-9	5 1/8"	Box	72/6
40	G30	Med.	<b>S3652</b>	40G30	Clear	120V	2500	384	CC-9	5 1/8"	Box	72/6
40	G30	Med.	<b>S3671</b>	40G30/W	White	120V	2500	320	CC-9	5 1/8"	Box	72/6
60	G30	Med.	<b>S3670</b>	60G30	Clear	120V	2500	650	CC-9	5 1/8"	Box	72/6
60	G30	Med.	<b>S3672</b>	60G30/W	White	120V	2500	575	CC-9	5 1/8"	Box	72/6

4000 Hours / 120 Volt

# Globe Lights 5"



**White**

- Medium Base
- S3000** 25 Watt
- S3001** 40 Watt
- S3002** 60 Watt
- S3003** 100 Watt
- S3004** 150 Watt

Packing: Individually Boxed  
24/Master, 6/Inner



**Clear**

- Medium Base
- S3010** 25 Watt
- S3011** 40 Watt
- S3012** 60 Watt
- S3013** 100 Watt
- S3014** 150 Watt

Packing: Individually Boxed  
24/Master, 6/Inner

Not Shown Actual Size


Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	G40	Med.	<b>S3010</b>	25G40	Clear	120V	4000	120	C-9	6 3/4"	Box	24/6
25	G40	Med.	<b>S3000</b>	25G40/W	White	120V	4000	110	C-9	6 3/4"	Box	24/6
40	G40	Med.	<b>S3011</b>	40G40	Clear	120V	4000	300	C-9	6 3/4"	Box	24/6
40	G40	Med.	<b>S3001</b>	40G40/W	White	120V	4000	280	C-9	6 3/4"	Box	24/6
60	G40	Med.	<b>S3012</b>	60G40	Clear	120V	4000	580	C-9	6 3/4"	Box	24/6
60	G40	Med.	<b>S3002</b>	60G40/W	White	120V	4000	550	C-9	6 3/4"	Box	24/6
100	G40	Med.	<b>S3013</b>	100G40	Clear	120V	4000	1150	C-9	6 3/4"	Box	24/6
100	G40	Med.	<b>S3003</b>	100G40/W	White	120V	4000	1050	C-9	6 3/4"	Box	24/6
150	G40	Med.	<b>S3014</b>	150G40	Clear	120V	4000	1700	C-9	6 3/4"	Box	24/6
150	G40	Med.	<b>S3004</b>	150G40/W	White	120V	4000	1550	C-9	6 3/4"	Box	24/6

decorative incandescent lamps

**Bulbs**

120 Volt / 1500 Hours

*Candelabra Base*



Clear

Clear

Clear

Clear

Clear

**S3272** 10 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**S3273** 15 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**S3274** 25 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**S3275** 40 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**S3262** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
10	CA-7	Cand.	<b>S3272</b>	10CA7	Clear	120V	1500	80	C-7A	3"	Box	500/25
15	CA-8	Cand.	<b>S3273</b>	15CA8	Clear	120V	1500	100	C-7A	3 5/8"	Box	500/25
25	CA-8	Cand.	<b>S3274</b>	25CA8	Clear	120V	1500	210	CC-2V	3 5/8"	Box	500/25
40	CA-9 1/2	Cand.	<b>S3275</b>	40CA9 1/2	Clear	120V	1500	370	CC-2V	3 15/16"	Box	500/25
60	CA-10	Cand.	<b>S3262</b>	60CA10	Clear	120V	1500	672	CC-2V	4 1/4"	Box	500/25

decorative incandescent lamps

*1500 Hours / 120 Volt*

*Candelabra Base*

decorative incandescent lamps



<b>S3263</b> 60 Watt Packing: Indiv. Boxed 500/Master, 25/Inner	<b>S3279</b> 40 Watt Packing: Indiv. Boxed 500/Master, 25/Inner	<b>S3278</b> 25 Watt Packing: Indiv. Boxed 500/Master, 25/Inner	<b>S3277</b> 15 Watt Packing: Indiv. Boxed 500/Master, 25/Inner	<b>S3276</b> 10 Watt Packing: Indiv. Boxed 500/Master, 25/Inner
---	---	---	---	---

*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
10	CA-7	Cand.	<b>S3276</b>	10CA7/F	Frosted	120V	1500	70	C7A	3"	Box	500/25
15	CA-8	Cand.	<b>S3277</b>	15CA8/F	Frosted	120V	1500	95	C7A	3 5/8"	Box	500/25
25	CA-8	Cand.	<b>S3278</b>	25CA8/F	Frosted	120V	1500	200	CC-2V	3 5/8"	Box	500/25
40	CA-9 1/2	Cand.	<b>S3279</b>	40CA9 1/2/F	Frosted	120V	1500	384	CC-2V	3 15/16"	Box	500/25
60	CA-10	Cand.	<b>S3263</b>	60CA10/F	Frosted	120V	1500	672	CC-2V	4 1/4"	Box	500/25

## Bulbs

### Candelabra Base



*Petite Clear*

**S3345** 15 Watt  
**S3346** 25 Watt  
**S3347** 40 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner



*Clear*

**S3230** 15 Watt  
**S3282** 25 Watt  
**S3283** 40 Watt  
**S3284** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner



*Frosted*

**S3291** 15 Watt  
**S3285** 25 Watt  
**S3286** 40 Watt  
**S3287** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner



*White*

**S3288** 25 Watt  
**S3289** 40 Watt  
**S3290** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner

### Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	B8	Cand.	<b>S3345</b>	15B8/Petite	Clear	130V	2500	114	C7A	3"	Box	500/25
15	B9 1/2	Cand.	<b>S3230</b>	15B9 1/2	Clear	120V	1500	114	C7A	3 1/2"	Box	500/25
15	B9 1/2	Cand.	<b>S3291</b>	15B9 1/2/F	Frosted	120V	1500	114	C7A	3 1/2"	Box	500/25
25	B8	Cand.	<b>S3346</b>	25B8/Petite	Clear	130V	2500	212	CC-2V	3"	Box	500/25
25	B9 1/2	Cand.	<b>S3282</b>	25B9 1/2	Clear	120V	1500	212	CC-2V	3 1/2"	Box	500/25
25	B9 1/2	Cand.	<b>S3285</b>	25B9 1/2/F	Frosted	120V	1500	212	CC-2V	3 1/2"	Box	500/25
25	B9 1/2	Cand.	<b>S3288</b>	25B9 1/2/W	White	120V	1500	180	CC-2V	3 1/2"	Box	500/25
40	B8	Cand.	<b>S3347</b>	40B8/Petite	Clear	130V	2500	384	CC-2V	3"	Box	500/25
40	B9 1/2	Cand.	<b>S3283</b>	40B9 1/2	Clear	120V	1500	384	CC-2V	3 1/2"	Box	500/25
40	B9 1/2	Cand.	<b>S3286</b>	40B9 1/2/F	Frosted	120V	1500	384	CC-2V	3 1/2"	Box	500/25
40	B9 1/2	Cand.	<b>S3289</b>	40B9 1/2/W	White	120V	1500	328	CC-2V	3 1/2"	Box	500/25
60	B10	Cand.	<b>S3284</b>	60B10	Clear	120V	1500	672	CC-2V	3 3/4"	Box	500/25
60	B10	Cand.	<b>S3287</b>	60B10/F	Frosted	120V	1500	672	CC-2V	3 3/4"	Box	500/25
60	B10	Cand.	<b>S3290</b>	60B10/W	White	120V	1500	630	CC-2V	3 3/4"	Box	500/25

decorative incandescent lamps



*1500 Hours / 120 Volt*

*Medium Base*



*White*

**S3237** 25 Watt  
**S3238** 40 Watt  
**S3299** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



*Frosted*

**S3234** 25 Watt  
**S3235** 40 Watt  
**S3296** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



*Clear*

**S3231** 25 Watt  
**S3232** 40 Watt  
**S3293** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B11	Med.	<b>S3231</b>	25B11	Clear	120V	1500	210	CC-2V	3 7/8"	Box	500/25
25	B11	Med.	<b>S3234</b>	25B11/F	Frosted	120V	1500	200	CC-2V	3 7/8"	Box	500/25
25	B11	Med.	<b>S3237</b>	25B11/W	White	120V	1500	150	CC-2V	3 7/8"	Box	500/25
40	B11	Med.	<b>S3232</b>	40B11	Clear	120V	1500	370	CC-2V	3 7/8"	Box	500/25
40	B11	Med.	<b>S3235</b>	40B11/F	Frosted	120V	1500	360	CC-2V	3 7/8"	Box	500/25
40	B11	Med.	<b>S3238</b>	40B11/W	White	120V	1500	330	CC-2V	3 7/8"	Box	500/25
60	B11	Med.	<b>S3293</b>	60B11	Clear	120V	1500	650	CC-2V	3 7/8"	Box	500/25
60	B11	Med.	<b>S3296</b>	60B11/F	Frosted	120V	1500	640	CC-2V	3 7/8"	Box	500/25
60	B11	Med.	<b>S3299</b>	60B11/W	White	120V	1500	580	CC-2V	3 7/8"	Box	500/25

decorative incandescent lamps

## Bulbs

120 Volt / 1500 Hours

Medium Base



Frosted

**S3267** 25 Watt  
**S3268** 40 Watt  
**S3269** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner



Clear

**S3264** 25 Watt  
**S3265** 40 Watt  
**S3266** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	CA-10	Med.	<b>S3264</b>	25CA10	Clear	120V	1500	210	CC-2V	4 1/4"	Box	500/25
25	CA-10	Med.	<b>S3267</b>	25CA10/F	Frosted	120V	1500	200	CC-2V	4 1/4"	Box	500/25
40	CA-10	Med.	<b>S3265</b>	40CA10	Clear	120V	1500	370	CC-2V	4 1/4"	Box	500/25
40	CA-10	Med.	<b>S3268</b>	40CA10/F	Frosted	120V	1500	360	CC-2V	4 1/4"	Box	500/25
60	CA-10	Med.	<b>S3266</b>	60CA10	Clear	120V	1500	650	CC-2V	4 1/4"	Box	500/25
60	CA-10	Med.	<b>S3269</b>	60CA10/F	Frosted	120V	1500	640	CC-2V	4 1/4"	Box	500/25

decorative incandescent lamps

*2500 Hours / 130 Volt*

*Candelabra Base*



**A3677** 15 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**A3678** 25 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**A3679** 40 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**A3663** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

*Shown Actual Size*

Watts	Bulb Type	Base	Satco		Finish	Volts	Avg. Rated		Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
			Order No.	Lamp Code			Hours	Lumens				
15	CA-8	Cand.	<b>A3677</b>	15CA8/F	Frosted	130V	2500	90	C-7A	3 5/8"	Box	500/25
25	CA-8	Cand.	<b>A3678</b>	25CA8/F	Frosted	130V	2500	200	CC-2V	3 5/8"	Box	500/25
40	CA-9 1/2	Cand.	<b>A3679</b>	40CA9 1/2/F	Frosted	130V	2500	350	CC-2V	3 15/16"	Box	500/25
60	CA-10	Cand.	<b>A3663</b>	60CA10/F	Frosted	130V	2500	635	CC-2V	4 1/4"	Box	500/25

decorative incandescent lamps

**Bulbs**

*130 Volt / 2500 Hours*

*Candelabra Base*



*Clear*

**A3673** 15 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



*Clear*

**A3674** 25 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



*Clear*

**A3675** 40 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



*Clear*

**A3662** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	CA-8	Cand.	<b>A3673</b>	15CA8	Clear	130V	2500	95	C-7A	3 5/8"	Box	500/25
25	CA-8	Cand.	<b>A3674</b>	25CA8	Clear	130V	2500	210	CC-2V	3 5/8"	Box	500/25
40	CA-9 1/2	Cand.	<b>A3675</b>	40CA9 1/2	Clear	130V	2500	370	CC-2V	3 15/16"	Box	500/25
60	CA-10	Cand.	<b>A3662</b>	60CA10	Clear	130V	2500	642	CC-2V	4 1/4"	Box	500/25

decorative incandescent lamps

2500 Hours / 130 Volt

Candelabra Base



Clear

Clear

Frosted

White

**A3620** 15 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**A3682** 25 Watt  
**A3683** 40 Watt  
**A3684** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**A3685** 25 Watt  
**A3686** 40 Watt  
**A3687** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**A3688** 25 Watt  
**A3689** 40 Watt  
**A3690** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	B9 1/2	Cand.	<b>A3620</b>	15B9 1/2	Clear	130V	2500	95	CC-2V	3 1/2"	Box	500/25
25	B9 1/2	Cand.	<b>A3682</b>	25B9 1/2	Clear	130V	2500	193	CC-2V	3 1/2"	Box	500/25
25	B9 1/2	Cand.	<b>A3685</b>	25B9 1/2/F	Frosted	130V	2500	193	CC-2V	3 1/2"	Box	500/25
25	B9 1/2	Cand.	<b>A3688</b>	25B9 1/2/W	White	130V	2500	163	CC-2V	3 1/2"	Box	500/25
40	B9 1/2	Cand.	<b>A3683</b>	40B9 1/2	Clear	130V	2500	384	CC-2V	3 1/2"	Box	500/25
40	B9 1/2	Cand.	<b>A3686</b>	40B9 1/2/F	Frosted	130V	2500	384	CC-2V	3 1/2"	Box	500/25
40	B9 1/2	Cand.	<b>A3689</b>	40B9 1/2/W	White	130V	2500	328	CC-2V	3 1/2"	Box	500/25
60	B10	Cand.	<b>A3684</b>	60B10	Clear	130V	2500	642	CC-2V	3 3/4"	Box	500/25
60	B10	Cand.	<b>A3687</b>	60B10/F	Frosted	130V	2500	642	CC-2V	3 3/4"	Box	500/25
60	B10	Cand.	<b>A3690</b>	60B10/W	White	130V	2500	564	CC-2V	3 3/4"	Box	500/25

decorative incandescent lamps

## Bulbs

130 Volt / 2500 Hours

Medium Base



White

**A3637** 25 Watt  
**A3638** 40 Watt  
**A3699** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner



Frosted

**A3634** 25 Watt  
**A3635** 40 Watt  
**A3696** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner



Clear

**A3631** 25 Watt  
**A3632** 40 Watt  
**A3693** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B11	Med.	<b>A3631</b>	25B11	Clear	130V	2500	210	CC-2V	3 7/8"	Box	500/25
25	B11	Med.	<b>A3634</b>	25B11/F	Frosted	130V	2500	200	CC-2V	3 7/8"	Box	500/25
25	B11	Med.	<b>A3637</b>	25B11/W	White	130V	2500	160	CC-2V	3 7/8"	Box	500/25
40	B11	Med.	<b>A3632</b>	40B11	Clear	130V	2500	370	CC-2V	3 7/8"	Box	500/25
40	B11	Med.	<b>A3635</b>	40B11/F	Frosted	130V	2500	360	CC-2V	3 7/8"	Box	500/25
40	B11	Med.	<b>A3638</b>	40B11/W	White	130V	2500	320	CC-2V	3 7/8"	Box	500/25
60	B11	Med.	<b>A3693</b>	60B11	Clear	130V	2500	650	CC-2V	3 7/8"	Box	500/25
60	B11	Med.	<b>A3696</b>	60B11/F	Frosted	130V	2500	640	CC-2V	3 7/8"	Box	500/25
60	B11	Med.	<b>A3699</b>	60B11/W	White	130V	2500	550	CC-2V	3 7/8"	Box	500/25

decorative incandescent lamps

*2500 Hours / 130 Volt*

*Medium Base*



*Clear*

**A3664** 25 Watt  
**A3665** 40 Watt  
**A3666** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



*Frosted*

**A3667** 25 Watt  
**A3668** 40 Watt  
**A3669** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	CA-10	Med.	<b>A3664</b>	25CA10	Clear	130V	2500	210	CC-2V	4 1/4"	Box	500/25
25	CA-10	Med.	<b>A3667</b>	25CA10/F	Frosted	130V	2500	200	CC-2V	4 1/4"	Box	500/25
40	CA-10	Med.	<b>A3665</b>	40CA10	Clear	130V	2500	370	CC-2V	4 1/4"	Box	500/25
40	CA-10	Med.	<b>A3668</b>	40CA10/F	Frosted	130V	2500	360	CC-2V	4 1/4"	Box	500/25
60	CA-10	Med.	<b>A3666</b>	60CA10	Clear	130V	2500	650	CC-2V	4 1/4"	Box	500/25
60	CA-10	Med.	<b>A3669</b>	60CA10/F	Frosted	130V	2500	640	CC-2V	4 1/4"	Box	500/25

decorative incandescent lamps

## Decorative bulbs

decorative incandescent lamps

**Torpedo**  
Euro Base E14

Specialty  
Product



**Clear**  
**S3390** 25 Watt  
**S3391** 40 Watt  
**S3392** 60 Watt



**Frosted**  
**S3380** 25 Watt  
**S3381** 40 Watt  
**S3382** 60 Watt

1500 Hrs. Average Life (120 Volt)  
Packing: Individually Boxed, 500/Master, 25/Inner

**Petite Turn-Tip 7½ Watt**  
Candelabra Base



**Clear**  
**S3241** 7½ Watt



**Frosted**  
**S3242** 7½ Watt



**Frosted/  
Yellow Tip**  
**S3243** 7½ Watt

1500 Hrs. Average Life (120 Volt)  
Packing: Indiv. Boxed, 2000/Master, 50/Inner

**7½ Watt**  
**"SHOWROOM"**  
**BULB**

Candelabra Base  
3000 Hrs. Average Life  
(120 Volt)

**Clear**  
**S4994** Torpedo  
**S4988** Turn Tip

Packing: Individually Boxed  
500/Master, 25/Inner

**Full Size/  
Low Wattage**  
Perfect for  
Fixture Displays



Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
7½	CA-5	Cand.	<b>S3241</b>	7½CA5	Clear	120V	1500	40	C-7A	2 7/8"	Box	2000/50
7½	CA-5	Cand.	<b>S3242</b>	7½CA5/F	Frosted	120V	1500	35	C-7A	2 7/8"	Box	2000/50
7½	CA-5	Cand.	<b>S3243</b>	7½CA5/FY	Frost. Yell.	120V	1500	35	C-7A	2 7/8"	Box	2000/50
7½	B9½	Cand.	<b>S4994</b>	7½B9½	Clear	120V	3000	37	C-7A	3 1/2"	Box	500/25
7½	C9½	Cand.	<b>S4988</b>	7½C9½	Clear	120V	3000	37	C-7A	3 1/2"	Box	500/25
25	B-9½	Euro. Base	<b>S3390</b>	25B9 ½/2	Clear	120V	1500	210	CC-2V	3 1/2"	Box	500/25
25	B-9½	Euro. Base	<b>S3380</b>	25B9 1/2/F	Frosted	120V	1500	200	CC-2V	3 1/2"	Box	500/25
40	B-9½	Euro. Base	<b>S3391</b>	40B9 ½/2	Clear	120V	1500	370	CC-2V	3 1/2"	Box	500/25
40	B-9½	Euro. Base	<b>S3381</b>	40B9 1/2/F	Frosted	120V	1500	360	CC-2V	3 1/2"	Box	500/25
60	B10	Euro. Base	<b>S3392</b>	60B10	Clear	120V	1500	650	CC-2V	3 3/4"	Box	500/25
60	B10	Euro. Base	<b>S3382</b>	60B10/F	Frosted	120V	1500	640	CC-2V	3 3/4"	Box	500/25





*Not Shown Actual Size*



**Silicone**

**S4520** 5 Watt  
Packing: Card/2  
144/Master, 12/Inner



**12V Clear**

**S3866** 7 Watt  
**S3867** 15 Watt  
**S3868** 25 Watt  
**S3869** 25 Watt  
Packing: 500/Master,  
25/Inner

decorative incandescent lamps

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
7	CA-10	Cand.	<b>S3866</b>	7CA10/CL/12V	Clear	12V	1500	65	CC-2V	4 1/4"	Box	500/25
15	CA-10	Cand.	<b>S3867</b>	15CA10/CL/12V	Frosted	12V	1500	150	CC-2V	4 1/4"	Box	500/25
25	CA-10	Cand.	<b>S3868</b>	25CA10/CL/12V	Clear	12V	1500	250	CC-2V	4 1/4"	Box	500/25
25	CA-10	Med.	<b>S3869</b>	25CA10/CL/12V	Clear	12V	1500	250	CC-2V	4 1/4"	Box	500/25
5	C-7	Cand.	<b>S4520</b>	5C7	Silicone	120V	1000	10	C-7A	2 1/2+"	2/Card	144/12

## Bulbs

120 Volt / 1500 Hours

### F10 Candelabra Base

Not Shown Actual Size



Clear

**S3360** 15 Watt  
**S3371** 25 Watt



White

**S3361** 15 Watt  
**S3372** 25 Watt



Aurora

**S3373** 25 Watt



Amber

**S3374** 25 Watt

Packing: Indiv. Boxed, 500/Master, 25/Inner

### F15

Medium Base



**S3363** 25 Watt Clear  
**S3367** 40 Watt Clear  
**S3364** 25 Watt White  
**S3368** 40 Watt White  
**S3365** 25 Watt Aurora  
**S3369** 40 Watt Aurora  
**S3366** 25 Watt Amber  
**S3370** 40 Watt Amber

Packing: Indiv. Boxed  
300/Master, 25/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	F10	Cand.	<b>S3360</b>	15F10	Clear	120V	1500	110	C-7A	3 1/16"	Box	500/25
15	F10	Cand.	<b>S3361</b>	15F10/W	White	120V	1500	90	C-7A	3 1/16"	Box	500/25
25	F10	Cand.	<b>S3371</b>	25F10	Clear	120V	1500	195	C-7A	3 1/16"	Box	500/25
25	F10	Cand.	<b>S3372</b>	25F10/W	White	120V	1500	185	C-7A	3 1/16"	Box	500/25
25	F10	Cand.	<b>S3373</b>	25F10/AU	Aurora	120V	1500	190	C-7A	3 1/16"	Box	500/25
25	F10	Cand.	<b>S3374</b>	25F10/A	Amber	120V	1500	n/a	C-7A	3 1/16"	Box	500/25
25	F15	Med.	<b>S3363</b>	25F15	Clear	120V	1500	225	CC-9	4 1/2"	Box	300/25
25	F15	Med.	<b>S3364</b>	25F15/W	White	120V	1500	195	CC-9	4 1/2"	Box	300/25
25	F15	Med.	<b>S3365</b>	25F15/AU	Aurora	120V	1500	200	CC-9	4 1/2"	Box	300/25
25	F15	Med.	<b>S3366</b>	25F15/A	Amber	120V	1500	n/a	CC-9	4 1/2"	Box	300/25
40	F15	Med.	<b>S3367</b>	40F15	Clear	120V	1500	420	CC-9	4 1/2"	Box	300/25
40	F15	Med.	<b>S3368</b>	40F15/W	White	120V	1500	372	CC-9	4 1/2"	Box	300/25
40	F15	Med.	<b>S3369</b>	40F15/AU	Aurora	120V	1500	420	CC-9	4 1/2"	Box	300/25
40	F15	Med.	<b>S3370</b>	40F15/A	Amber	120V	1500	n/a	CC-9	4 1/2"	Box	300/25



*Krypton decorative bulbs create a brilliant sparkle, similar to the look of halogen. Excellent for use in crystal chandeliers and fixtures with decorative glassware.*

*Additionally, Krypton bulbs last longer than conventional lamps and maintain their lumen output during the full course of their life.*

**2500 Hours** **Bulbs**

*Not Shown Actual Size*



**G16 1/2**

**Torpedo**

**Flame**

**Torpedo**

**Clear**

- S4471** 25 Watt
- S4472** 40 Watt
- S4473** 60 Watt

*Packing: Indiv. Boxed  
500/Master, 25/Inner*

**Clear**

- S4995** 25Watt
- S4996** 40 Watt
- S4997** 60 Watt

*Packing: Indiv. Boxed  
500/Master, 25/Inner*

**Clear**

- S4465** 25 Watt
- S4466** 40 Watt
- S4467** 60 Watt

*Packing: Indiv. Boxed  
500/Master, 25/Inner*

**Clear**

- S4468** 25Watt
- S4469** 40 Watt
- S4470** 60 Watt

*Packing: Indiv. Boxed  
500/Master, 25/Inner*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack Type	Mst. Ctn./ Inner Pack
25	B9 1/2	Cand.	<b>S4995</b>	KR25B9 1/2	Clear	120V	2500	212	CC-2V	3 7/8"	Box	500/25
25	CA-9 1/2	Cand.	<b>S4465</b>	KR25CA9 1/2	Clear	120V	2500	212	CC-2V	3 15/16"	Box	500/25
25	B11	Med.	<b>S4468</b>	KR25B11	Clear	120V	2500	212	CC-2V	3 7/8"	Box	500/25
25	G16 1/2	Cand.	<b>S4471</b>	KR25G16 1/2	Clear	120V	2500	212	CC-2V	3"	Box	500/25
40	B-9 1/2	Cand.	<b>S4996</b>	KR40B9 1/2	Clear	120V	2500	380	CC-2V	3 7/8"	Box	500/25
40	CA-9 1/2	Cand.	<b>S4466</b>	KR40CA9 1/2	Clear	120V	2500	380	CC-2V	3 15/16"	Box	500/25
40	B11	Med.	<b>S4469</b>	KR40B11	Clear	120V	2500	380	CC-2V	3 7/8"	Box	500/25
40	G16 1/2	Cand.	<b>S4472</b>	KR40G16 1/2	Clear	120V	2500	380	CC-2V	3"	Box	500/25
60	B10	Cand.	<b>S4997</b>	KR60B11	Clear	120V	2500	720	CC-2V	3 7/8"	Box	500/25
60	CA-10	Cand.	<b>S4467</b>	KR60CA-10	Clear	120V	2500	720	CC-2V	4 1/4"	Box	500/25
60	B11	Med.	<b>S4470</b>	KR60B11	Clear	120V	2500	720	CC-2V	3 7/8"	Box	500/25
60	G16 1/2	Cand.	<b>S4473</b>	KR60G16 1/2	Clear	120V	2500	720	CC-2V	3"	Box	500/25

decorative incandescent lamps

**Bulbs**

120 Volt / 4000 Hours

decorative incandescent lamps



**C15**

**Amber**  
Medium Base  
**S3416** 40 Watt  
Packing: Individually Boxed  
300/Master, 25/Inner



**C15**

**Satin**  
Medium Base  
**S3413** 25 Watt  
**S3414** 40 Watt  
**S3415** 60 Watt  
Packing: Individually Boxed  
300/Master, 25/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	C15	Med.	<b>S3413</b>	25C15	Satin	120V	4000	160	C-9	4 1/2"	Box	300/25
40	C15	Med.	<b>S3414</b>	40C15	Satin	120V	4000	316	C-9	4 1/2"	Box	300/25
40	C15	Med.	<b>S3416</b>	40C15/A	Amber	120V	4000	n/a	C-9	4 1/2"	Box	300/25
60	C15	Med.	<b>S3415</b>	60C15	Satin	120V	4000	606	C-9	4 1/2"	Box	300/25

4000 Hours / 120Volts

**Bulbs**



**C11**

**C11**

**Satin**

Candelabra Base

**S3403** 25 Watt

**S3404** 40 Watt

**S3405** 60 Watt

Packing: Individually Boxed  
500/Master, 25/Inner

**Amber**

Candelabra Base

**S3406** 25 Watt

Packing: Individually Boxed  
500/Master, 25/Inner

**Satco-Escent®**  
bulbs simulate the feel and charm of an old style gas light. The unique silk like threading wraps around the bulbs and enhances the image of the filament into an elongated glow. Perfect for use in outdoor lanterns and exposed bulb chandeliers.

*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated		Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
						Volts	Hours					
25	C11	Cand.	<b>S3403</b>	25C11	Satin	120V	4000	160	C-7A	4"	Box	500/25
25	C11	Cand.	<b>S3406</b>	25C11/A	Amber	120V	4000	n/a	C-7A	4"	Box	500/25
40	C11	Cand.	<b>S3404</b>	40C11	Satin	120V	4000	316	C-7A	4"	Box	500/25
60	C11	Cand.	<b>S3405</b>	60C11	Satin	120V	4000	606	C-7A	4"	Box	500/25

decorative incandescent lamps

## Bulbs

120 Volt / 1000 Hours

decorative incandescent lamps



Candelabra Base

**S3661** 3 Watt



Candelabra Base

**S3656** 3 Watt



Candelabra Base

**S3659** 3 Watt



Medium Base

**S3657** 3 Watt



Medium Base

**S3660** 3 Watt

Packing: Individually Boxed  
500/Master, 25/Inner

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
3	CA-5 1/2	Cand.	<b>S3661</b>	3CA5 1/2/FLK	Clear	120V	1000	n/a	Flicker	3 1/4"	Box	500/25
3	CA-8	Cand.	<b>S3659</b>	3CA8/FLK	Clear	120V	1000	n/a	Flicker	3 7/8"	Box	500/25
3	B-9 1/2	Cand.	<b>S3656</b>	3B9 1/2/FLK	Clear	120V	1000	n/a	Flicker	3 1/2"	Box	500/25
3	CA-10	Med.	<b>S3657</b>	3CA10/FLK	Clear	120V	1000	n/a	Flicker	4 1/16"	Box	500/25
3	CA-9	Med.	<b>S3660</b>	3CA9/FLK	Clear	120V	1000	n/a	Flicker	4 9/16"	Box	500/25

1500 Hours / 120 Volt

Candelabra Base



*Clear*



*Frosted*



*Aurora*

Candelabra Base  
**S3744** 25 Watt  
**S3745** 40 Watt  
 Packing: Card/2  
 120 Master, 12 Inner

Candelabra Base  
**S3746** 25 Watt  
**S3747** 40 Watt  
 Packing: Card/2  
 120 Master, 12 Inner

Candelabra Base  
**S3748** 25 Watt  
**S3749** 40 Watt  
 Packing: Card/2  
 120 Master, 12 Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Volts	Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	HX-10 1/2	Cand.	<b>S3744</b>	25HX10 1/2	Clear	120V	1500	175	C-7A	4 15/16"	Card/2	120/12
25	HX-10 1/2	Cand.	<b>S3746</b>	25HX10 1/2/F	Frosted	120V	1500	175	C-7A	4 15/16"	Card/2	120/12
25	HX-10 1/2	Cand.	<b>S3748</b>	25HX10 1/2/AU	Aurora	120V	1500	175	C-7A	4 15/16"	Card/2	120/12
40	HX-10 1/2	Cand.	<b>S3745</b>	40HX10 1/2	Clear	120V	1500	360	C-7A	4 15/16"	Card/2	120/12
40	HX-10 1/2	Cand.	<b>S3747</b>	40HX10 1/2/F	Frosted	120V	1500	360	C-7A	4 15/16"	Card/2	120/12
40	HX-10 1/2	Cand.	<b>S3749</b>	40HX10 1/2/AU	Aurora	120V	1500	360	C-7A	4 15/16"	Card/2	120/12

decorative incandescent lamps

# Torpedo

120 Volt / 1500 Hours



**Amber**  
Candelabra Base

**S3813** 25 Watt  
**S3818** 40 Watt  
**S3819** 60 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner



**Red**  
Candelabra Base

**S3219** 25 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner



**Blue**  
Candelabra Base

**S3218** 25 Watt  
 Packing: Indiv. Boxed  
 500/Master, 25/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B-91/2	Cand.	<b>S3218</b>	25B91/2/B	Blue	120V	1500	n/a	CC-2V	3 1/2"	Box	500/25
25	B-91/2	Cand.	<b>S3219</b>	25B91/2/R	Red	120V	1500	n/a	CC-2V	3 1/2"	Box	500/25
25	B-91/2	Cand.	<b>S3813</b>	25B91/2/A	Amber	120V	1500	n/a	CC-2V	3 1/2"	Box	500/25
40	B-91/2	Cand.	<b>S3818</b>	40B91/2/A	Amber	120V	1500	n/a	CC-2V	3 1/2"	Box	500/25
60	B-91/2	Cand.	<b>S3819</b>	60B91/2/A	Amber	120V	1500	n/a	CC-2V	3 1/2"	Box	500/25

decorative incandescent lamps



# Night



## Light bulbs

Brass Base

Candelabra Base



### 7C7

Candelabra Base  
(120 Volt)

**S3691** 7 Watt Clear

**S3692** 7 Watt White

Packing: Bulk  
2000/Master, 25/Box

Shown Actual Size



### 4C7

Candelabra Base (120 Volt)

**S3680** 4 Watt Clear

**S3681** 4 Watt White

Packing: Bulk  
2000/Master, 50/Box

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
4	C7	Cand.	<b>S3680</b>	4C7	Clear	120V	3000	16	C-7A	2 1/8"	Bulk	2000/50
4	C7	Cand.	<b>S3681</b>	4C7/W	White	120V	3000	8	C-7A	2 1/8"	Bulk	2000/50
7	C7	Cand.	<b>S3691</b>	7C7	Clear	120V	3000	35	C-7A	2 1/8"	Bulk	2000/25
7	C7	Cand.	<b>S3692</b>	7C7/W	White	120V	3000	20	C-7A	2 1/8"	Bulk	2000/25

general service lamps

**2500 Hours**



**7 1/2 S11**

Medium Base  
2500 Hrs. Average Life  
(120 Volt)

- S3606** 7 1/2 Watt Clear
- S3607** 7 1/2 Watt Glossy White
- S3608** 7 1/2 Watt Ceramic Blue
- S3609** 7 1/2 Watt Ceramic Green
- S3610** 7 1/2 Watt Ceramic Orange
- S3611** 7 1/2 Watt Ceramic Red

Packing: Individually Boxed  
1000/Master, 25/Inner



**11 S14**

Medium Base  
2500 Hrs. Average Life  
(130 Volt)

- S3965** 11 Watt Clear
- S3960** 11 Watt Ceramic Yellow
- S3961** 11 Watt Ceramic Red
- S3962** 11 Watt Ceramic Green
- S3963** 11 Watt Ceramic Blue
- S3964** 11 Watt Ceramic Orange
- S3966** 11 Watt Frosted

Packing: 4 Pack Sleeve, 120/Master



*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
7 1/2	S11	Med.	<b>S3606</b>	7 1/2 S11	Clear	120V	2500	40	C-7A	2 1/4"	Sleeve	1000/25
7 1/2	S11	Med.	<b>S3607</b>	7 1/2 S11/W	White	120V	2500	25	C-7A	2 1/4"	Sleeve	1000/25
7 1/2	S11	Med.	<b>S3608</b>	7 1/2 S11/B	Blue	120V	2500	n/a	C-7A	2 1/4"	Sleeve	1000/25
7 1/2	S11	Med.	<b>S3609</b>	7 1/2 S11/G	Green	120V	2500	n/a	C-7A	2 1/4"	Sleeve	1000/25
7 1/2	S11	Med.	<b>S3610</b>	7 1/2 S11/O	Orange	120V	2500	n/a	C-7A	2 1/4"	Sleeve	1000/25
7 1/2	S11	Med.	<b>S3611</b>	7 1/2 S11/R	Red	120V	2500	n/a	C-7A	2 1/4"	Sleeve	1000/25
11	S14	Med.	<b>S3965</b>	11 S14	Clear	130V	2500	80	CC-9	3 1/2"	Sleeve	120/4
11	S14	Med.	<b>S3966</b>	11 S14/F	Frost.	130V	2500	65	CC-9	3 1/2"	Sleeve	120/4
11	S14	Med.	<b>S3963</b>	11 S14/B	Blue	130V	2500	n/a	CC-9	3 1/2"	Sleeve	120/4
11	S14	Med.	<b>S3962</b>	11 S14/G	Green	130V	2500	n/a	CC-9	3 1/2"	Sleeve	120/4
11	S14	Med.	<b>S3964</b>	11 S14/O	Orange	130V	2500	n/a	CC-9	3 1/2"	Sleeve	120/4
11	S14	Med.	<b>S3961</b>	11 S14/R	Red	130V	2500	n/a	CC-9	3 1/2"	Sleeve	120/4
11	S14	Med.	<b>S3960</b>	11 S14/Y	Yellow	130V	2500	n/a	CC-9	3 1/2"	Sleeve	120/4

# T10 Tubular *Brass Base*



## *Bulbs*

*120 Volt / 1000 Hours*

*Medium Base*

general service lamps



*Clear*

Medium Base  
(120 Volt)  
**S3250** 25 Watt  
**S3252** 40 Watt  
**S3896** 60 Watt  
Packing: Individually Boxed  
500/Master, 25/Inner



*Frosted*

Medium Base  
(120 Volt)  
**S3251** 25 Watt  
**S3253** 40 Watt  
**S3899** 60 Watt  
Packing: Individually Boxed  
500/Master, 25/Inner

*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	T10	Med.	<b>S3250</b>	25T10	Clear	120V	1000	210	C-5V	5 3/16"	Box	500/25
25	T10	Med.	<b>S3251</b>	25T10/F	Frosted	120V	1000	200	C-5V	5 3/16"	Box	500/25
40	T10	Med.	<b>S3252</b>	40T10	Clear	120V	1000	300	C-5V	5 3/16"	Box	500/25
40	T10	Med.	<b>S3253</b>	40T10/F	Frosted	120V	1000	290	C-5V	5 3/16"	Box	500/25
60	T10	Med.	<b>S3896</b>	60T10	Clear	120V	1000	490	C-5V	5 3/16"	Box	500/25
60	T10	Med.	<b>S3899</b>	60T10/F	Frosted	120V	1000	480	C-5V	5 3/16"	Box	500/25

*1500 Hours / 130 Volt*

*D.C. Bayonet Base*

*Shown Actual Size*



**Clear**



**Frosted**

*D.C. Bayonet Base  
(130 Volt)*

**S3297** 20 Watt  
**S3248** 25 Watt

*Packing: Individually Boxed  
500/Master, 25/Inner*

*D.C. Bayonet Base  
(130 Volt)*

**S3298** 20 Watt  
**S3249** 25 Watt

*Packing: Individually Boxed  
500/Master, 25/Inner*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
20	T6 <sup>1</sup> / <sub>2</sub>	DC BAY	<b>S3297</b>	20T6 <sup>1</sup> / <sub>2</sub> DC	Clear	130V	1500	150	C-8	5 3/8"	Box	500/25
20	T6 <sup>1</sup> / <sub>2</sub>	DC BAY	<b>S3298</b>	20T6 <sup>1</sup> / <sub>2</sub> DC/F	Frosted	130V	1500	140	C-8	5 3/8"	Box	500/25
25	T6 <sup>1</sup> / <sub>2</sub>	DC BAY	<b>S3248</b>	25T6 <sup>1</sup> / <sub>2</sub> DC	Clear	130V	1500	180	C-8	5 3/8"	Box	500/25
25	T6 <sup>1</sup> / <sub>2</sub>	DC BAY	<b>S3249</b>	25T6 <sup>1</sup> / <sub>2</sub> DC/F	Frosted	130V	1500	170	C-8	5 3/8"	Box	500/25



# T6<sup>1</sup>/<sub>2</sub> Tubular *Brass Base*



## *Bulbs*

**130 Volt / 1500 Hours**

*Intermediate Base*

*Shown Actual Size*



**Clear**



**Frosted**

*Intermediate Base  
(130 Volt)*

- S3280** 20 Watt Clear
- S3222** 25 Watt Clear
- S3224** 40 Watt Clear

*Packing: Individually Boxed  
500/Master, 25/Inner*

*Intermediate Base  
(130 Volt)*

- S3281** 20 Watt Frosted
- S3223** 25 Watt Frosted
- S3225** 40 Watt Frosted

*Packing: Individually Boxed  
500/Master, 25/Inner*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
20	T61/2	Int.	<b>S3280</b>	20T61/2N	Clear	130V	1500	150	C-8	5 3/8"	Box	500/25
20	T61/2	Int.	<b>S3281</b>	20T61/2N/IF	Frosted	130V	1500	140	C-8	5 3/8"	Box	500/25
25	T61/2	Int.	<b>S3222</b>	25T61/2N	Clear	130V	1500	180	C-8	5 3/8"	Box	500/25
25	T61/2	Int.	<b>S3223</b>	25T61/2N/IF	Frosted	130V	1500	170	C-8	5 3/8"	Box	500/25
40	T61/2	Int.	<b>S3224</b>	40T61/2N	Clear	130V	1500	350	C-8	5 3/8"	Box	500/25
40	T61/2	Int.	<b>S3225</b>	40T61/2N/IF	Frosted	130V	1500	340	C-8	5 3/8"	Box	500/25

general service lamps



Shown Actual Size



Intermediate Base  
115-125 Volt

**S3621** 10 Watt  
Dom. Code #10S11N

**S3628** 15 Watt  
Dom. Code #15S11N

**S3630** 25 Watt  
Dom. Code #25S11N

**S3629** 40 Watt  
Dom. Code #40S11N

Packing: Individually Boxed  
600/Master, 10/Inner



**S3624** 24 Watt/15CP  
SC Bayonet Base/6-8V  
Dom. Code #1133

Packing: Individually Boxed  
600/Master, 10/Inner



**S3623** 12 Watt/15CP  
SC Bayonet Base/12-16V  
Dom. Code #93

Packing: Individually Boxed  
600/Master, 10/Inner



**S1383** 20 Watt/20 CP  
S.C. Bayonet Base 13 Volt

Packing: Individually Boxed  
600/Master, 10/Inner



**S3622** 10 Watt  
Intermediate Base/115-125V  
Dom. Code #10S11N/F

Packing: Individually Boxed  
600/Master, 10/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
12	S8	S.C.BAY.	<b>S3623</b>	12S8/93	Clear	12-16V	200	190	C-6	2 "	Box	600/10
10	S11	Int.	<b>S3621</b>	10S11/N	Clear	115/125V	1500	80	C-7A	2 3/8"	Box	600/10
10	S11	Int.	<b>S3622</b>	10S11N/F	Frosted	115/125V	1500	80	CC-2V	2 3/8"	Box	600/10
15	S11	Int.	<b>S3628</b>	15S11/N	Clear	115/125V	1500	100	C-7A	2 3/8"	Box	600/10
25	S11	Int.	<b>S3630</b>	25S11/N	Clear	115/125V	1500	210	CC-2V	2 3/8"	Box	600/10
40	S11	Int.	<b>S3629</b>	40S11/N	Clear	115/125V	1500	370	CC-2V	2 3/8"	Box	600/10
24	RP11	S.C.BAY.	<b>S3624</b>	24RP11/1133	Clear	6/8V	300	400	C-6	2 1/4"	Box	600/10
20	R-11 1/2	S.C.BAY.	<b>S1383</b>	20R111/2/1383	Frosted	13V	600	200	C-6	2 1/2"	Box	600/10
20	R-11 1/2	S.C.BAY.	<b>S1383/TF</b>	20R111/2/1383	Shtr Prof	13V	600	200	C-6	2 1/2"	Box	600/10

## Bulbs *Shown Actual Size*

**2500 Hours**



**Indicator Bulb**  
**S3911** 15 Watt  
 Int. Base/130 Volt  
 Dom. Code #15T7/N



**Appliance Bulb**  
**S3905** 15 Watt  
 Cand. Base/130 Volt  
 Dom. Code #15T7C



**Appliance Bulb**  
**S3908** 25 Watt  
 Int. Base/130 Volt  
 Dom. Code #25T8N



**Indicator Bulb**  
**S3907** 25 Watt  
 Cand. Base/130 Volt  
 Dom. Code #25T8C



**Indicator Bulb**  
**S3906** 15 Watt  
 D.C. Bay. Base/130 Volt  
 Dom. Code #15T7/DC



**Indicator Bulb**  
**S3909** 25 Watt  
 D.C. Bay. Base/130 Volt  
 Dom. Code #25T8DC



**Microwave Bulb**  
**S3917** 40 Watt  
 Int. Base/130 Volt  
 Dom. Code #40T8N  
 Packing: 1/Card  
 120/Master, 12/Inner

Packing: 10 Pack Sleeve  
 120/Master, 10/Inner

**Appliance • Indicator • Switchboard • Night Light**

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	T7	Int.	<b>S3911</b>	15T7/N	Clear	130V	2500	95	C-5A	2 1/4"	Sleeve	120/10
15	T7	Cand.	<b>S3905</b>	15T7	Clear	130V	2500	95	C-5A	2 1/4"	Sleeve	120/10
15	T7	DC Bayonet	<b>S3906</b>	15T7/DC	Clear	130V	2500	95	C-5A	2 1/4"	Sleeve	120/10
25	T8	Cand.	<b>S3907</b>	25T8	Clear	130V	2500	190	C-5A	2 5/8"	Sleeve	120/10
25	T8	Int.	<b>S3908</b>	25T8/N	Clear	130V	2500	190	C-5A	2 5/8"	Sleeve	120/10
25	T8	DC Bayonet	<b>S3909</b>	25T8/DC	Clear	130V	2500	190	C-5A	2 5/8"	Sleeve	120/10
40	T8	Int.	<b>S3917</b>	40T8N	Clear	130V	2500	370	CC-2V	2 5/8"	1/Card	120/12

general service lamps

**2500 Hours**

Shown Actual Size



**Appliance Bulb**  
**S3901** 6 Watt  
 D.C. Bay. Base  
 130 Volt  
 Dom. Code #6S6DC



**Indicator Bulb**  
**S3900** 6 Watt  
 Cand. Base  
 130 Volt  
 Dom. Code #6S6

- Appliance
- Indicator
- Switchboard
- Night Light
- Picture Light



**Appliance Bulb**  
**S3904** 10 Watt  
 D.C. Bay. Base  
 130 Volt  
 Dom. Code #10C7DC



**Night Light**  
**S3902** 7 Watt  
 Cand. Base/130 Volt  
 Dom. Code #7C7  
**S3903** 10 Watt  
 Cand. Base/130 Volt  
 Dom. Code #10C7



**Switchboard Bulb**  
**S3910** 15 Watt  
 Cand. Base/130 Volt  
 Dom. Code #15T6  
**S3912** 15 Watt  
 Cand. Base/145 Volt  
 Dom. Code #15T6  
**S3315** 15 Watt  
 Cand. Base/120 Volt  
 Dom. Code #15T6/F

Packing: 10 Pack Sleeve  
 120/Master, 10/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
6	S6	Cand.	<b>S3900</b>	6S6	Clear	130V	2500	30	C-7A	1 7/8"	Sleeve	120/10
6	S6	DC Bayonet	<b>S3901</b>	6S6/DC	Clear	130V	2500	30	C-7A	1 7/8"	Sleeve	120/10
7	C7	Cand.	<b>S3902</b>	7C7	Clear	130V	2500	35	C-7A	1 7/8"	Sleeve	120/10
10	C7	Cand.	<b>S3903</b>	10C7	Clear	130V	2500	60	C-7A	2 1/8"	Sleeve	120/10
10	C7	DC Bayonet	<b>S3904</b>	10C7/DC	Clear	130V	2500	60	C-7A	2 1/8"	Sleeve	120/10
15	T6	Cand.	<b>S3910</b>	15T6	Clear	130V	2500	95	C-5A	3 1/16"	Sleeve	120/10
15	T6	Cand.	<b>S3912</b>	15T6	Clear	145V	2500	95	C-5A	3 1/16"	Sleeve	120/10
15	T6	Cand.	<b>S3315</b>	15T6/F	Frost	120V	2500	95	C-5A	4"	Sleeve	500/25

general service lamps





# NEW PRODUCT INFORMATION

## Vintage style incandescent lamps

Historically accurate.  
Beautifully reproduced.

Satco's Vintage Lamps are truthful, historic reproductions from this important and ever-popular era in lighting and architecture. No detail is overlooked, making these high-quality lamps the perfect solution when achieving authenticity and atmosphere are the goals.

### Features


- Classic, warm glow from clearly visible filaments
- Historic restoration quality
- Perfect for hotel, theater, restaurants and other themed venues
- Authentic reproductions display beautifully
- Attractive full color packaging



S2411, S2412,  
S2419



S2413,  
S2423



S2414



S2415



S2416



S2417



S2418



S2420




S2421,  
S2422

**NEW**

Available  
February 2014



S2424



S2425



# NEW PRODUCT INFORMATION

Item Number	Lamp Description	Wattage	Coil Design	Volts	Base	Finish	Hours	Lumens	Master/Inner
S2411	25A19/CL/120V VINTAGE	25	Quad Loop	120V	E26	Clear	3000	50	48/6
S2412	40A19/CL/120V VINTAGE	40	Quad Loop	120V	E26	Clear	3000	130	48/6
S2419	60A19/CL/120V VINTAGE	60	Quad Loop	120V	E26	Clear	3000	240	48/6
S2413	40ST19/CL/15S/120V VINTAGE	40	Cage Style	120V	E26	Clear	3000	135	48/6
S2414	40ST19/CL/9S/120V VINTAGE	40	Hairpin	120V	E26	Clear	3000	165	48/6
S2415	20T9/CL/120V VINTAGE	20	Hairpin	120V	E26	Clear	3000	20	48/6
S2416	40T14/CL/32S/120V VINTAGE	40	Spiral	120V	E26	Clear	3000	135	50/10
S2417	40T14/CL/15S/120V VINTAGE	40	Cage Style	120V	E26	Clear	3000	135	50/10
S2418	25CFC/7S/120V VINTAGE	25	Deco Carbon	120V	E12	Clear	3000	45	50/10
S2420	40T9/GOLD/9S/120V VINTAGE	40	Cage Style	120V	E12	Gold	3000	20	50/10
S2421	40T9/CL/12S/120V VINTAGE	40	Hairpin	120V	E26	Clear	3000	160	50/10
S2422	60T9/CL/12S/120V VINTAGE	60	Hairpin	120V	E26	Clear	3000	230	50/10
S2423	60ST19/CL/15S/120V VINTAGE	60	Cage Style	120V	E26	Clear	3000	240	48/6
S2424	40A15/CL/13S/120V VINTAGE	40	Cage Style	120V	E26	Clear	2000	160	50/10
S2425	40G25/CL/15S/120V VINTAGE	40	Cage Style	120V	E26	Clear	3000	160	48/6



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



# NEW PRODUCT INFORMATION

## Vintage Style LED filament lamps

### Features

- LED with a traditional vintage look and feel
- Amber finish
- Omni-directional light source
- Smooth dimming
- 2200 & 2300K - warm tone color temperature
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp location
- Approved for totally enclosed fixtures
- cUL listed



S9577,  
S9578, S9579  
ST19



S9584  
G25



S9583  
A19



S9585  
ST19



S9586  
C35



S9587  
CA35



S9588  
T9

### LED Filament Lamps



Item Number	Lamp Description	W	Bulb Type	Base	V	Finish	CCT	Lm	CRI	M.O.L. (Inches)	Life/ Hrs.	UPC
S9577	2.5ST19/AMB/LED/E26/23K/120V	2.5	ST19	E26	120	Amber	2300K	220	80	5 3/8	15K	045923095771
S9578	4.5ST19/AMB/LED/E26/23K/120V	4.5	ST19	E26	120	Amber	2300K	400	80	5 3/8	15K	045923095788
S9579	6.5ST19/AMB/LED/E26/23K/120V	6.5	ST19	E26	120	Amber	2300K	650	80	5 3/8	15K	045923095795
S9583	4.5A19/AMB/LED/E26/22K/120V	4.5	A19	E26	120	Amber	2200K	380	80	4 1/8	15K	045923095832
S9584	4.5G25/AMB/LED/E26/22K/120V	4.5	G25	E26	120	Amber	2200K	380	80	4 3/8	15K	045923095849
S9585	4.5ST19/AMB/LED/E26/22K/120V	4.5	ST19	E26	120	Amber	2200K	380	80	5 1/2	15K	045923095856
S9586	4CTA/LED/AMB/22K/120V	4	C35	E12	120	Amber	2200K	300	80	4 5/16	15K	045923095863
S9587	4CFA/LED/AMB/22K/120V	4	CA35	E12	120	Amber	2200K	300	80	5	15K	045923095870
S9588	6.5T9/AMB/LED/E26/22K/120V	6.5	T9	E26	120	Amber	2200K	620	80	12	15K	045923095887

Pack: Master 24 / Inner 6/1

# LED SPECIALTY LAMPS

## LED filament lamps

### Applications / Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp location
- Approved for totally enclosed fixtures
- cUL listed



### LED Filament Lamps




Item Number	Lamp Description	W	Bulb Type	Base	V	Finish	CCT	Lm	CRI	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9560	4.5A15/CL/LED/E26/27K/120V	4.5	A15	E26	120	Clear	2700K	450	80	3 3/8	15K	045923095603	24/6
S9561	4.5A19/CL/LED/E26/27K/120V	4.5	A19	E26	120	Clear	2700K	450	80	4 1/8	15K	045923095610	24/6
S9562	6.5A19/CL/LED/E26/27K/120V	6.5	A19	E26	120	Clear	2700K	810	80	4 1/8	15K	045923095627	24/6
S9563*	4.5G25/CL/LED/E26/27K/120V	4.5	G25	E26	120	Clear	2700K	450	80	4 3/8	25K	045923095634	24/6
S9564	6.5G25/CL/LED/E26/27K/120V	6.5	G25	E26	120	Clear	2700K	810	80	4 3/8	15K	045923095641	24/6
S9565	4.5G40/CL/LED/E26/27K/120V	4.5	G40	E26	120	Clear	2700K	450	80	6 1/2	15K	045923095658	24/6
S9566	6.5G40/CL/LED/E26/27K/120V	6.5	G40	E26	120	Clear	2700K	810	80	6 1/2	15K	045923095665	24/6
S9820+	2W CTC/LED/27K/CL/120V/AG	2	C35	E12	120	Clear	2700K	190	80	3 7/8	15K	045923098208	24/6
S9821+	2W CFC/LED/27K/CL/120V/AG	2	CA35	E12	120	Clear	2700K	190	80	4 11/16	15K	045923098215	24/6
S9822+	4W CTC/LED/27K/CL/120V/AG	4	C35	E12	120	Clear	2700K	340	80	3 7/8	15K	045923098222	24/6
S9823+	4W CFC/LED/27K/CL/120V/AG	4	CA35	E12	120	Clear	2700K	340	80	4 11/16	15K	045923098239	24/6
S9567*	2.5W ETC/LED/27K/120V	2.5	C35	E26	120	Clear	2700K	250	80	3 1/2	15K	045923095672	24/6
S9568*	2.5W CTC/LED/27K/120V	2.5	C35	E12	120	Clear	2700K	250	80	4 5/16	15K	045923095689	24/6
S9569*	4.5W ETC/LED/27K/120V	4.5	C35	E26	120	Clear	2700K	450	80	3 1/2	15K	045923095696	24/6
S9570*	4.5W CTC/LED/27K/120V	4.5	C35	E12	120	Clear	2700K	450	80	4 5/16	15K	045923095702	24/6
S9571	2.5W EFC/LED/27K/120V	2.5	CA35	E26	120	Clear	2700K	250	80	4 5/16	15K	045923095719	24/6
S9572	2.5W CFC/LED/27K/120V	2.5	CA35	E12	120	Clear	2700K	250	80	5	15K	045923095726	24/6
S9573	4.5W EFC/LED/27K/120V	4.5	CA35	E26	120	Clear	2700K	450	80	4 5/16	15K	045923095733	24/6
S9574	4.5W CFC/LED/27K/120V	4.5	CA35	E12	120	Clear	2700K	450	80	5	15K	045923095740	24/6
S9575	4.5BT15/CL/LED/E26/27K/120V	4.5	BT15	E26	120	Clear	2700K	450	80	4 1/8	15K	045923095757	24/6
S9576	6.5BT15/CL/LED/E26/27K/120V	6.5	BT15	E26	120	Clear	2700K	810	80	4 1/8	15K	045923095764	24/6
S9581	6.5ST19/CL/LED/E26/27K/120V	6.5	ST19	E26	120	Clear	2700K	810	80	5 1/2	15K	045923095818	24/6
S9582	6.5T9/CL/LED/E26/27K/120V	6.5	T9	E26	120	Clear	2700K	800	80	12	15K	045923095825	24/6
S9580	4.5T10/LED/E26/27K/120V	4.5	T10	E26	120	Clear	2700K	430	80	5	15K	045923095801	24/6

\*AG - All glass envelope



## VINTAGE STYLE Incandescent

Historically Accurate Bulbs all beautifully reproduced



- Classic warm glow from clearly visible filaments
- Historic restoration quality
- Perfect for hotel, theater, restaurants & other themed venues
- Authentic reproductions display beautifully.
- Attractive full - color packaging

ITEM NUMBER	DESCRIPTION	WATTAGE	COIL DESIGN	VOLTS	BASE	FINISH	HOURS	LUMENS	CARTON	EACH	MASTER
S2411	25A19/CL/120V VINTAGE	25	Quad Loop	120V	E26	Clear	3000	50	48/6	\$5.55	\$4.85
S2412	40A19/CL/120V VINTAGE	40	Quad Loop	120V	E26	Clear	3000	130	48/6	\$5.55	\$4.85
S2413	40ST19/CL/15S/120V VINTAGE	40	Cage Style	120V	E26	Clear	3000	135	48/6	\$5.65	\$4.95
S2414	40ST19/CL/9S/120V VINTAGE	40	Hairpin	120V	E26	Clear	3000	165	48/6	\$5.65	\$4.95
S2415	20T9/CL/120V VINTAGE	20	Hairpin	120V	E26	Clear	3000	20	48/6	\$5.45	\$4.75
S2416	40T14/CL/32S/120V VINTAGE	40	Spiral	120V	E26	Clear	3000	135	50/10	\$5.65	\$4.95
S2417	40T14/CL/15S/120V VINTAGE	40	Cage Style	120V	E26	Clear	3000	135	50/10	\$5.65	\$4.95
S2418	25CFC/7S/120V VINTAGE	25	Deco Carbon	120V	E12	Clear	3000	45	50/10	\$3.95	\$3.25



National Toll-Free: 1-800-43-SATCO (1-800-437-2826)

Visit Our Web Site at: [www.satco.com](http://www.satco.com)

Also see us on



EXECUTIVE OFFICES & WAREHOUSE; NEW YORK, 110 Heartland Blvd., Brentwood, NY 11717 • 800-437-2826 • (631) 243-2022 • FAX (631) 243-2027  
 FLORIDA, 900 N.W. 159th Drive, Miami, FL 33169 • 800-437-2826 • (305) 624-2044 • FAX (305) 623-0286  
 TEXAS, 2000 Valwood Parkway, Farmers branch, TX 75234 • 800-437-2826 • (972) 247-2437 • FAX (972) 247-5408  
 CALIFORNIA, 31288 San Benito St., Hayward, CA 94544 • 800-437-2826 • (510) 487-4822 • FAX (510) 487-8955  
 WASHINGTON, 4710 116th St. S.W., Mukilteo, WA 98275 • 800-437-2826 • (425) 789-3300 • FAX (425) 789-3310  
 PUERTO RICO, Bldg 3, Campeche St. 23 Julio N. Matos Industrial Park • Bo Martin Gonzales Carolina, PR 00984 • (787) 757-3510 • FAX (787) 757-3540

Not responsible for typographical errors.

## Fan *Bulbs*

130 Volt / 2500 Hours



*Frosted*

Medium Base  
**S3815** 25 Watt  
**S3811** 40 Watt  
**S3871** 60 Watt

Packing: Individually Boxed  
 500 Master, 25/Inner



*Clear*

Medium Base  
**S3814** 25Watt  
**S3810** 40 Watt  
**S3870** 60 Watt

Packing: Individually Boxed  
 500 Master, 25/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	A15	Med.	<b>S3814</b>	25A15	Clear	130V	2500	130	C-9	3 1/2"	Box	500/25
25	A15	Med.	<b>S3815</b>	25A15/F	Frosted	130V	2500	120	C-9	3 1/2"	Box	500/25
40	A15	Med.	<b>S3810</b>	40A15	Clear	130V	2500	290	C-9	3 1/2"	Box	500/25
40	A15	Med.	<b>S3811</b>	40A15/F	Frosted	130V	2500	280	C-9	3 1/2"	Box	500/25
60	A15	Med.	<b>S3870</b>	60A15	Clear	130V	2500	580	C-9	3 1/2"	Box	500/25
60	A15	Med.	<b>S3871</b>	60A15/F	Frosted	130V	2500	530	C-9	3 1/2"	Box	500/25

general service lamps

2500 Hours / 130 Volts

Medium Base



Clear

Medium Base  
**S3948** 15 Watt  
Packing: Boxed, 2 Pack  
120 Master, 60 2-Packs  
Sold Per Lamp



Frosted

Medium Base  
**S3949** 15 Watt  
Packing: Boxed, 2 Pack  
120 Master, 60 2-Packs  
Sold Per Lamp



general service lamps

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
15	A15	Med.	<b>S3948</b>	15A15	Clear	130V	2500	100	C-9	3 1/2"	Box/2	120
15	A15	Med.	<b>S3949</b>	15A15/F	Frosted	130V	2500	100	C-9	3 1/2"	Box/2	120

# A19 Household Brass Base



## Lamps 2 Pack

120 Volt / 1500 Hours

Medium Base



Clear



Frosted



Not Shown  
Actual Size

Medium Base

- S6040** 25 Watt
- S6041** 40 Watt
- S6042** 60 Watt
- S6043** 75 Watt
- S6044** 100 Watt

Packing: Boxed, 2 Pack  
120 Master, 60 2-Packs  
Sold Per Lamp

Medium Base

- S6050** 25 Watt
- S6051** 40 Watt
- S6052** 60 Watt
- S6053** 75 Watt
- S6054** 100 Watt

Packing: Boxed, 2 Pack  
120 Master, 60 2-Packs  
Sold Per Lamp

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack Type	Mst.Ctn.
25	A19	Med.	<b>S6040</b>	25A19	Clear	120V	1500	185	C-9	4 1/8"	Box/2	120
25	A19	Med.	<b>S6050</b>	25A19/F	Frosted	120V	1500	185	C-9	4 1/8"	Box/2	120
40	A19	Med.	<b>S6041</b>	40A19	Clear	120V	1500	340	C-9	4 1/8"	Box/2	120
40	A19	Med.	<b>S6051</b>	40A19/F	Frosted	120V	1500	340	C-9	4 1/8"	Box/2	120
60	A19	Med.	<b>S6042</b>	60A19	Clear	120V	1500	610	C-9	4 1/8"	Box/2	120
60	A19	Med.	<b>S6052</b>	60A19/F	Frosted	120V	1500	610	C-9	4 1/8"	Box/2	120
75	A19	Med.	<b>S6043</b>	75A19	Clear	120V	1500	800	C-9	4 1/8"	Box/2	120
75	A19	Med.	<b>S6053</b>	75A19/F	Frosted	120V	1500	800	C-9	4 1/8"	Box/2	120
100	A19	Med.	<b>S6044</b>	100A19	Clear	120V	1500	1150	C-9	4 1/8"	Box/2	120
100	A19	Med.	<b>S6054</b>	100A19/F	Frosted	120V	1500	1150	C-9	4 1/8"	Box/2	120

general service lamps



# A19 Household Lamps 2 Pack

2500 Hours / 130 Volt

Medium Base

Not Shown  
Actual Size



**Frosted**



**Clear**



Medium Base

- S3950** 25 Watt
- S3951** 40 Watt
- S3952** 60 Watt
- S3953** 75 Watt
- S3954** 100 Watt

Packing: Boxed, 2 Pack  
120 Master, 60 2-Packs  
Sold Per Lamp

Medium Base

- S3940** 25 Watt
- S3941** 40 Watt
- S3942** 60 Watt
- S3943** 75 Watt
- S3944** 100 Watt

Packing: Boxed, 2 Pack  
120 Master, 60 2-Packs  
Sold Per Lamp

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack Type	Mst.Ctn.
25	A19	Med.	<b>S3940</b>	25A19	Clear	130V	2500	185	CC-6	4 1/8"	Box/2	120
25	A19	Med.	<b>S3950</b>	25A19/F	Frosted	130V	2500	185	CC-6	4 1/8"	Box/2	120
40	A19	Med.	<b>S3941</b>	40A19	Clear	130V	2500	320	C-9	4 1/8"	Box/2	120
40	A19	Med.	<b>S3951</b>	40A19/F	Frosted	130V	2500	320	C-9	4 1/8"	Box/2	120
60	A19	Med.	<b>S3942</b>	60A19	Clear	130V	2500	580	C-9	4 1/8"	Box/2	120
60	A19	Med.	<b>S3952</b>	60A19/F	Frosted	130V	2500	580	C-9	4 1/8"	Box/2	120
75	A19	Med.	<b>S3943</b>	75A19	Clear	130V	2500	760	C-9	4 1/8"	Box/2	120
75	A19	Med.	<b>S3953</b>	75A19/F	Frosted	130V	2500	760	C-9	4 1/8"	Box/2	120
100	A19	Med.	<b>S3944</b>	100A19	Clear	130V	2500	1100	C-9	4 1/8"	Box/2	120
100	A19	Med.	<b>S3954</b>	100A19/F	Frosted	130V	2500	1100	C-9	4 1/8"	Box/2	120

**130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE**

23	A19	Med.	<b>S3940</b>	25A19	Clear	130V	5000	140	CC-6	4 1/8"	Box/2	120
23	A19	Med.	<b>S3950</b>	25A19/F	Frosted	130V	5000	140	CC-6	4 1/8"	Box/2	120
36	A19	Med.	<b>S3941</b>	40A19	Clear	130V	5000	235	C-9	4 1/8"	Box/2	120
36	A19	Med.	<b>S3951</b>	40A19/F	Frosted	130V	5000	235	C-9	4 1/8"	Box/2	120
53	A19	Med.	<b>S3942</b>	60A19	Clear	130V	5000	445	C-9	4 1/8"	Box/2	120
53	A19	Med.	<b>S3952</b>	60A19/F	Frosted	130V	5000	445	C-9	4 1/8"	Box/2	120
66	A19	Med.	<b>S3943</b>	75A19	Clear	130V	5000	570	C-9	4 1/8"	Box/2	120
66	A19	Med.	<b>S3953</b>	75A19/F	Frosted	130V	5000	570	C-9	4 1/8"	Box/2	120
90	A19	Med.	<b>S3944</b>	100A19	Clear	130V	5000	810	C-9	4 1/8"	Box/2	120
90	A19	Med.	<b>S3954</b>	100A19/F	Frosted	130V	5000	810	C-9	4 1/8"	Box/2	120

general service lamps

# A19 Household Brass Base



## Lamps 4 Pack

120 Volt / 1500 Hours

Medium Base



Not Shown  
Actual Size

### Soft White

Medium Base

**S1810** 40 Watt

**S1811** 60 Watt

**S1812** 75 Watt

**S1813** 100 Watt

Packing: Boxed, Pack

48 Master, 12 4-Packs

Sold Per Lamp



### Frosted

Medium Base

**S1711** 40 Watt

**S1712** 60 Watt

**S1713** 75 Watt

**S1714** 100 Watt

Packing: Boxed, 4 Pack

48 Master, 12 4-Packs

Sold Per Lamp



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
40	A19	Med.	<b>S1711</b>	40A19/F	Frosted	120V	1500	340	C-9	4 1/8"	Box/4	48
40	A19	Med.	<b>S1810</b>	40A19/W	White	120V	1500	280	C-9	4 1/8"	Box/4	48
60	A19	Med.	<b>S1712</b>	60A19/F	Frosted	120V	1500	610	C-9	4 1/8"	Box/4	48
60	A19	Med.	<b>S1811</b>	60A19/W	White	120V	1500	500	C-9	4 1/8"	Box/4	48
75	A19	Med.	<b>S1713</b>	75A19/F	Frosted	120V	1500	800	C-9	4 1/8"	Box/4	48
75	A19	Med.	<b>S1812</b>	75A19/W	White	120V	1500	650	C-9	4 1/8"	Box/4	48
100	A19	Med.	<b>S1714</b>	100A19/F	Frosted	120V	1500	1150	C-9	4 1/8"	Box/4	48
100	A19	Med.	<b>S1813</b>	100A19/W	White	120V	1500	950	C-9	4 1/8"	Box/4	48

general service lamps

Not Shown Actual Size

Medium Base **Lamps**



**Long Life  
Commercial Service**

**Frosted**     **S3934** 75 Watt A21  
 Medium Base     **S3935** 100 Watt A21  
                          **S3936** 100 Watt A23

Packing: Individually Sleeved  
 120 Master, 6/Inner

**Long Neck A Lamps**

- 130 Volt Frosted
- 12,500 Hrs. Avg. Life (when burned at 120v).
- Resists Power Surges.



**Left Hand  
Thread A19**

**Frosted**     **S6010** 100 Watt  
 Medium Base

Packing: Individually Sleeved  
 120 Master, 6/Inner

- Left-hand thread to prevent theft.
- Uses: construction, work sites, hotels, restaurants, etc.

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
100	A19	Med.	<b>S6010</b>	100A19/LHT/F	Frosted	120V	2000	1200	C-9	4 1/8"	Sleeve	120/6
75	A21	Med.	<b>S3934</b>	75A21/IF/130V	Frosted	130V	5000	680	C-9	5 5/16"	Sleeve	120/6
100	A21	Med.	<b>S3935</b>	100A21/IF/130V	Frosted	130V	5000	1030	C-9	5 5/16"	Sleeve	120/6
100	A23	Med.	<b>S3936</b>	100A23/IF/130V	Frosted	130V	5000	1030	C-9	6 1/16"	Sleeve	120/6

**130 Volt Bulb Specifications Operated On a 120 Volt Line**

66	A21	Med.	<b>S3934</b>	75A21/IF/130V	Frosted	130V	12,500	515	C-9	5 5/16"	Sleeve	120/6
88	A21	Med.	<b>S3935</b>	100A21/IF/130V	Frosted	130V	12,500	780	C-9	5 5/16"	Sleeve	120/6
88	A23	Med.	<b>S3936</b>	100A23/IF/130V	Frosted	130V	12,500	780	C-9	6 1/16"	Sleeve	120/6

# A19 Specialty Brass Base



## Lamps

Medium Base

Not Shown Actual Size



### Incandescent Black Light

Medium Base  
120 Volt /480 Hrs. Avg. Life  
**S3920** 75 Watt  
Packing: Individually Boxed  
96 Master, 6/Inner

### Bug Light

Medium Base  
130 Volt /2000 Hrs. Avg. Life  
**S3859** 40 Watt Yellow  
**S3938** 60 Watt Yellow  
**S3939** 100 Watt Yellow  
Packing: Boxed, 2 Pack  
24 Master, 12 2-Packs  
Sold Per Lamp

### Silver Crown

Medium Base  
130 Volt /1500 Hrs. Avg. Life  
**S3955** 60A19/SL  
**S3956** 100A19/SL  
Packing: Individually Boxed  
24 Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
40	A19	Med.	<b>S3859</b>	40A/Y	Bug	130V	2000	-	C-9	4 1/8"	Box/2	24
60	A19	Med.	<b>S3938</b>	60A/Y	Bug	130V	2000	-	C-9	4 1/8"	Box/2	24
100	A19	Med.	<b>S3939</b>	100A/Y	Bug	130V	2000	-	C-9	4 1/8"	Box/2	24
75	A19	Med.	<b>S3920</b>	75A/BL	Black Light	120V	480	-	C-9	4 1/8"	Box	96/6
60	A19	Med.	<b>S3955</b>	60A/SL	Silver	130V	1500	580	C-9	4 1/8"	Box	24
100	A19	Med.	<b>S3956</b>	100A/SL	Silver	130V	1500	960	C-9	4 1/8"	Box	24

general service lamps

*1000 Hours*

**A19** Transparent

*Medium Base*



**25W**  
Medium Base 130 Volt

**S6080** Transparent Red  
**S6081** Transparent Green  
**S6082** Transparent Blue  
**S6083** Transparent Yellow  
 Packing: Individually Sleeved  
 24/Master, 12 Inner

*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	A19	Med.	<b>S6080</b>	25A/TR	Red	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
25	A19	Med.	<b>S6081</b>	25A/TG	Green	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
25	A19	Med.	<b>S6082</b>	25A/TB	Blue	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
25	A19	Med.	<b>S6083</b>	25A/TY	Yellow	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12

general service lamps

# Party *Bulbs* Brass Base



## A19 Ceramic

1000 Hours

Medium Base

Not Shown Actual Size



**25W**  
Medium Base  
130 Volt

- S6090** Ceramic Red
- S6091** Ceramic Green
- S6092** Ceramic Blue
- S6093** Ceramic Yellow

Packing: Individually Sleeved  
24/Master, 12 Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	A19	Med.	<b>S6090</b>	25A/R	Red	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
25	A19	Med.	<b>S6091</b>	25A/G	Green	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
25	A19	Med.	<b>S6092</b>	25A/B	Blue	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
25	A19	Med.	<b>S6093</b>	25A/Y	Yellow	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12

specialty lamps

*1000 Hours*

*Medium Base*

*Not Shown Actual Size*



**40W**  
Medium Base  
130 Volt

**S4980** Ceramic Red  
**S4981** Ceramic Blue  
**S4982** Ceramic Green  
**S4983** Ceramic Yellow  
Packing: Individually Boxed  
24/Master, 12/Inner

**60W**  
Medium Base  
130 Volt

**S4984** Ceramic Red  
**S4985** Ceramic Blue  
**S4986** Ceramic Green  
**S4987** Ceramic Yellow  
Packing: Individually Boxed  
24/Master, 12/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
40	A19	Med.	<b>S4980</b>	40A/R	Cer. Red	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
40	A19	Med.	<b>S4981</b>	40A/B	Cer. Blue	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
40	A19	Med.	<b>S4982</b>	40A/G	Cer. Green	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
40	A19	Med.	<b>S4983</b>	40A/Y	Cer. Yellow	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
60	A19	Med.	<b>S4984</b>	60A/R	Cer. Red	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
60	A19	Med.	<b>S4985</b>	60A/B	Cer. Blue	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
60	A19	Med.	<b>S4986</b>	60A/G	Cer. Green	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12
60	A19	Med.	<b>S4987</b>	60A/Y	Cer. Yellow	130V	1000	n/a	C-9	4 1/8"	Sleeve	24/12

specialty lamps

# A19 Household Lamps 3 Pack



130 Volt



Sold Per Pack  
Full Cases Only

Not Shown Actual Size

Soft White

Medium Base

**S3991** 40 Watt

**S3992** 60 Watt

**S3993** 75 Watt

**S3994** 100 Watt

Packing: Boxed, 3 Pack  
120 Master, 40 3-Packs

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
40	A19	Med.	<b>S3991</b>	40A19/W	White	130V	1250	288	C-9	4 1/8"	Box/3	40
60	A19	Med.	<b>S3992</b>	60A19/W	White	130V	1250	576	C-9	4 1/8"	Box/3	40
75	A19	Med.	<b>S3993</b>	75A19/W	White	130V	1250	747	C-9	4 1/8"	Box/3	40
100	A19	Med.	<b>S3994</b>	100A19/W	White	130V	1250	1107	C-9	4 1/8"	Box/3	40

general service lamps





# A19 Household Lamps 4 Pack

130 Volt



**Clear**

**Soft White**

Sold Per Pack  
Full Cases Only

Medium Base

- S4020** 40 Watt
- S4021** 60 Watt
- S4022** 75 Watt
- S4023** 100 Watt

Packing: Boxed, 4 Pack  
120 Master, 30 4-Packs

Medium Base

- S4010** 40 Watt
- S4011** 60 Watt
- S4012** 75 Watt
- S4013** 100 Watt

Packing: Boxed, 4 Pack  
120 Master, 30 4-Packs

Not Shown  
Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn.
40	A19	Med.	<b>S4020</b>	40A19	Clear	130V	1000	320	C-9	4 1/8"	Box/4	30
40	A19	Med.	<b>S4010</b>	40A19/W	White	130V	1000	288	C-9	4 1/8"	Box/4	30
60	A19	Med.	<b>S4021</b>	60A19	Clear	130V	1000	640	C-9	4 1/8"	Box/4	30
60	A19	Med.	<b>S4011</b>	60A19/W	White	130V	1000	576	C-9	4 1/8"	Box/4	30
75	A19	Med.	<b>S4022</b>	75A19	Clear	130V	1000	830	C-9	4 1/8"	Box/4	30
75	A19	Med.	<b>S4012</b>	75A19/W	White	130V	1000	747	C-9	4 1/8"	Box/4	30
100	A19	Med.	<b>S4023</b>	100A19	Clear	130V	1000	1230	C-9	4 1/8"	Box/4	30
100	A19	Med.	<b>S4013</b>	100A19/W	White	130V	1000	1107	C-9	4 1/8"	Box/4	30

### 130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE

36	A19	Med.	<b>S4020</b>	40A19	Clear	130V	3000	230	C-9	4 1/8"	Box/4	30
36	A19	Med.	<b>S4010</b>	40A19/W	White	130V	3000	207	C-9	4 1/8"	Box/4	30
53	A19	Med.	<b>S4021</b>	60A19	Clear	130V	3000	460	C-9	4 1/8"	Box/4	30
53	A19	Med.	<b>S4011</b>	60A19/W	White	130V	3000	414	C-9	4 1/8"	Box/4	30
66	A19	Med.	<b>S4022</b>	75A19	Clear	130V	3000	598	C-9	4 1/8"	Box/4	30
66	A19	Med.	<b>S4012</b>	75A19/W	White	130V	3000	538	C-9	4 1/8"	Box/4	30
90	A19	Med.	<b>S4023</b>	100A19	Clear	130V	3000	885	C-9	4 1/8"	Box/4	30
90	A19	Med.	<b>S4013</b>	100A19/W	White	130V	3000	797	C-9	4 1/8"	Box/4	30

general service lamps



# A19 Safety Coated



## Shatterproof *Lamps* Brass Base 130 Volt

Medium Base



- Rubber coating contains glass particles should bulb break.
- Heavy duty shatter proof bulb.
- Long life.
- Resists power surges – 130V.
- Five support filament to withstand vibration and impact.
- Uses: Workshops, garages, construction areas, bathrooms, or any hazardous environments



**Frosted**

Medium Base

**S3927** 60 Watt

**S3928** 75 Watt

**S3929** 100 Watt

Packing: Boxed, 2 Pack  
12 Master, 12 2-Packs  
Sold Per Pack

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
60	A19	Med.	<b>S3927</b>	60A19/RS/TF	Frosted	130V	5000	520	C-9	4 1/8"	2/Pks	12
75	A19	Med.	<b>S3928</b>	75A19/RS/TF	Frosted	130V	5000	680	C-9	4 1/8"	2/Pks	12
100	A19	Med.	<b>S3929</b>	100A19/RS/TF	Frosted	130V	5000	960	C-9	4 1/8"	2/Pks	12
<b>130 Volt Bulb Specifications Operated On a 120 Volt Line</b>												
53	A19	Med.	<b>S3927</b>	60A19/RS/TF	Frosted	130V	12,500	395	C-9	4 1/8"	2/Pks	12
66	A19	Med.	<b>S3928</b>	75A19/RS/TF	Frosted	130V	12,500	515	C-9	4 1/8"	2/Pks	12
88	A19	Med.	<b>S3929</b>	100A19/RS/TF	Frosted	130V	12,500	730	C-9	4 1/8"	2/Pks	12

general service lamps



**Safety Coated**

Medium Base  
A21 130 Volt  
**S3972** 75 Watt  
**S3973** 100 Watt  
Packing: Boxed, 2 Pack,  
24 Master, 12 2-Packs  
Sold Per Pack



**Rough Service**

Medium Base  
A19 130 Volt  
**S3969** 50 Watt  
**S3970** 75 Watt  
**S3971** 100 watt  
Packing: Boxed, 2 Pack,  
24 Master, 12 2-Packs  
Sold Per Pack

*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
50	A19	Med.	<b>S3969</b>	50A/RS	Frost	130V	2500	320	C-9	4 1/8"	Box/2	24
75	A19	Med.	<b>S3970</b>	75A/RS	Frost	130V	2500	620	C-9	4 1/8"	Box/2	24
100	A19	Med.	<b>S3971</b>	100A/RS	Frost	130V	2500	880	C-9	4 1/8"	Box/2	24
75	A21	Med.	<b>S3972</b>	75A21/TF	Frost	130V	2500	620	C-9	5 5/16"	Box/2	24
100	A21	Med.	<b>S3973</b>	100A21/TF	Frost	130V	2500	880	C-9	5 5/16"	Box/2	24

general service lamps



# 3-Way



## Household Lamps

Not Shown Actual Size



**3 Way/Med.**

**Soft White**  
 Medium Base  
 120 Volt  
**S1820** 30/70/100 Watt  
**S1821** 50/100/150 Watt  
**S1823** 50/200/250 Watt  
 Packing: Individually Sleeved  
 36/Master, 12/Inner



**3 Way/Mogul**

**Soft White**  
 Mogul Base  
 120 Volt  
**S1822** 100/300 Watt  
 Packing: Individually Sleeved  
 12/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
30								250	CC-2V	5 1/16"	Sleeve	36/12
70	A21	Med. Brass	<b>S1820</b>	30/70/100A21/W	White	120V	2500	700	C-9			
100								950				
50								520	CC-2V	5 1/16"	Sleeve	36/12
100	A21	Med. Brass	<b>S1821</b>	50/100/150A21/W	White	120V	2500	1050	C-9			
150								1570				
50								640	CC-8	5 1/16"	Sleeve	12
200	A21	Med. Alum.	<b>S1823</b>	50/200/250A21/W	White	120V	1200	3300	CC-8			
250								3940				
100								1385	CC-8			
200	PS25	Mog. Alum.	<b>S1822</b>	100/200/300PS25/W	White	120V	1200	3540	CC-8	6 3/4"	Sleeve	12
300								4925				

general service lamps

# 3-Way Household Lamps

Medium Base



BRILLIANT  
WHITE  
LIGHT

EXTRA  
LONG  
LIFE!

**HALOGEN**

Dual halogen capsules create 3 light levels

Not Shown Actual Size



**REDUCED SIZE  
A19 3 WAY**

**3-Way Halogen Reading Light**

**A19 3-Way**

**Soft White/4000 Hours**  
Medium Base  
120 Volt  
**S4505** 30/70/100 Watt  
**S4506** 50/100/150 Watt  
Packing: Individually Sleeved  
36/Master, 12/Inner

**Soft White**  
Medium Base  
120 Volt  
**S1824** 30/70/100 Watt  
Packing: Individually Sleeved  
36/Master, 12/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Flament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
30								250	CC-8			
70	A19	Med. Brass	<b>S1824</b>	30/70/100A19/W	White	120V	2500	700	CC-8	4 1/8"	Sleeve	36/12
100								950				
30								295	CC-8			
70	A21	Med. Alum.	<b>S4505</b>	30/70/100A21/HAL/W	White	120V	4000	785	CC-8	5 1/16"	Sleeve	36/12
100								1080				
50								385	CC-8			
100	A21	Med. Alum.	<b>S4506</b>	50/100/150A21/HAL/W	White	120V	4000	1400	CC-8	5 1/16"	Sleeve	36/12
150								1985				

general service lamps



# A21 Household Brass Base



## Lamps

2500 HOURS/130 Volt

Medium Base

Not Shown Actual Size

general service lamps



**Clear**

Medium Base  
130 Volt  
**S3981** 150 Watt  
Packing:  
Individually Boxed  
24/Master



**Frosted**

Medium Base  
130 Volt  
**S3980** 150 Watt  
Packing:  
Individually Boxed  
24/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
150	A21	Med.	<b>S3981</b>	150A21	Clear	130V	2500	1750	C-9	5 1/16"	Box	24
150	A21	Med.	<b>S3980</b>	150A21/F	Frosted	130V	2500	1750	C-9	5 1/16"	Box	24
<b>130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE</b>												
134	A21	Med.	<b>S3981</b>	150A21	Clear	130V	6000	1350	C-9	5 1/16"	Box	24
134	A21	Med.	<b>S3980</b>	150A21/F	Frosted	130V	6000	1350	C-9	5 1/16"	Box	24

2500 Hours / 130 Volt

**Lamps**

Not Shown Actual Size

Medium Base



**Frosted**



**Clear**

Medium Base  
130 Volt  
**S3982** 200 Watt  
Packing:  
Individually Boxed  
24/Master

Medium Base  
130 Volt  
**S3983** 200 Watt  
Packing:  
Individually Boxed  
24/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
200	A23	Med.	<b>S3983</b>	200A23	Clear	130V	2500	2500	C-9	6 1/16"	Box	24
200	A23	Med.	<b>S3982</b>	200A23/F	Frosted	130V	2500	2500	C-9	6 1/16"	Box	24
<b>130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE</b>												
179	A23	Med.	<b>S3983</b>	200A23	Clear	130V	6000	1750	C-9	6 1/16"	Box	24
179	A23	Med.	<b>S3982</b>	200A23/F	Frosted	130V	6000	1750	C-9	6 1/16"	Box	24

general service lamps



# PS25 General Brass Base



## Service Lamps

2500 Hours/130 Volt

Not Shown Actual Size



Clear

Medium Base  
300M 130 Volt  
**S4959** 300 Watt  
Packing:  
Individually Boxed  
24/Master



Frosted

Medium Base  
300M/IF 130 Volt  
**S4960** 300 Watt  
Packing:  
Individually Boxed  
24/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
300	PS25	Med.	<b>S4959</b>	300M	Clear	130V	2500	3600	C-9	6 <sup>15</sup> / <sub>16</sub> "	Box	24
300	PS25	Med.	<b>S4960</b>	300M/IF	Frosted	130V	2500	3600	C-9	6 <sup>15</sup> / <sub>16</sub> "	Box	24

### 130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE

264	PS25	Med.	<b>S4959</b>	300M	Clear	130V	5000	2640	C-9	6 <sup>15</sup> / <sub>16</sub> "	Box	24
264	PS25	Med.	<b>S4960</b>	300M/IF	Frosted	130V	5000	2640	C-9	6 <sup>15</sup> / <sub>16</sub> "	Box	24

general service lamps



2500 Hours/130 Volt

Service **Lamps**

Not Shown Actual Size



**Clear**

Mogul Base  
300 130 Volt  
**S4961** 300 Watt  
Packing:  
Individually Boxed  
12/Master



**Frosted**

Mogul Base  
300IF 130 Volt  
**S4962** 300 Watt  
Packing:  
Individually Boxed  
12/Master

general service lamps

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
300	PS35	Mog.	<b>S4961</b>	300	Clear	130V	2500	3600	C-9	93/8"	Box	12
300	PS35	Mog.	<b>S4962</b>	300/IF	Frosted	130V	2500	3600	C-9	93/8"	Box	12

**130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE**

264	PS35	Mog.	<b>S4961</b>	300	Clear	130V	5000	2640	C-9	93/8"	Box	12
264	PS35	Mog.	<b>S4962</b>	300/IF	Frosted	130V	5000	2640	C-9	93/8"	Box	12

# A19 Energy Saver



## Lamps Aluminum Base

Medium Base

Not Shown Actual Size



**Energy Saver**  
**130 Volt**

**Frosted**  
Medium Base

- S4990** 40A/34
- S4991** 60A/52
- S4992** 75A/67
- S4993** 100A/90

Packing: Boxed, 4 Pack,  
48/Master, 12 4-Packs



**Energy Saver**  
**120 Volt**

**Frosted**  
Medium Base

- S4460** 40A/34
- S4461** 60A/52
- S4462** 75A/67
- S4463** 100A/90

Packing: Boxed, 4 Pack,  
48/Master, 12 4-Packs

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn.
34	A19	Med.	<b>S4990</b>	40A/34	Frosted	130V	1500	375	CC-8	4 7/16"	Box/4	48
34	A19	Med.	<b>S4460</b>	40A/34	Frosted	120V	1500	385	CC-8	4 7/16"	Box/4	48
52	A19	Med.	<b>S4991</b>	60A/52	Frosted	130V	1000	740	CC-8	4 7/16"	Box/4	48
52	A19	Med.	<b>S4461</b>	60A/52	Frosted	120V	1000	745	CC-8	4 7/16"	Box/4	48
67	A19	Med.	<b>S4992</b>	75A/67	Frosted	130V	750	1065	CC-8	4 7/16"	Box/4	48
67	A19	Med.	<b>S4462</b>	75A/67	Frosted	120V	750	1040	CC-8	4 7/16"	Box/4	48
90	A19	Med.	<b>S4993</b>	100A/90	Frosted	130V	750	1550	CC-8	4 7/16"	Box/4	48
90	A19	Med.	<b>S4463</b>	100A/90	Frosted	120V	750	1520	CC-8	4 7/16"	Box/4	48
<b>130 VOLT BULB SPECIFICATIONS ON 120 VOLT LINE</b>												
26	A19	Med.	<b>S4990</b>	40A/34	Frosted	130V	3750	285	CC-8	4 7/16"	Box/4	48
46	A19	Med.	<b>S4991</b>	60A/52	Frosted	130V	3750	550	CC-8	4 7/16"	Box/4	48
59	A19	Med.	<b>S4992</b>	75A/67	Frosted	130V	1875	770	CC-8	4 7/16"	Box/4	48
79	A19	Med.	<b>S4993</b>	100A/90	Frosted	130V	1875	1125	CC-8	4 7/16"	Box/4	48

general service lamps

# Linear Incandescent Lamps

Not Shown Actual Size




**T8**  
Medium Base



**T8**  
Disc Base



**T8**  
Disc Base



**T10**  
S14S Base

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
40	T8	Med.	<b>S2977</b>	40T8	Clear	130V	2000	265	C-8	12"	Box	10
60	T8	Med.	<b>S2978</b>	60T8	Clear	130V	2000	425	C-8	12"	Box	10
75	T8	Med.	<b>S2979</b>	75T8	Clear	130V	2000	584	C-8	12"	Box	10
40	T8	Disc	<b>S2980</b>	L40	Clear	120V	1500	325	C-8	11 3/4"	Sleeve	24
40	T8	Disc	<b>S2981</b>	L40W	White	120V	1500	295	C-8	11 3/4"	Sleeve	12
60	T8	Disc	<b>S2982</b>	L60	Clear	120V	1500	480	C-8	17 3/4"	Sleeve	24
60	T8	Disc	<b>S2983</b>	L60W	White	120V	1500	450	C-8	17 3/4"	Sleeve	12
60	T10	S14S	<b>S4894</b>	LN60	White	125V	1000	460	C-8	19 11/16"	Box	25
150	T10	S14S	<b>S4895</b>	LN150	White	125V	1000	930	C-8	39 1/8"	Sleeve	16

# Natural Spectrum

## 120 Volt / 2000 Hours **Neodymium** Lamps

**Natural Spectrum Lamps** utilize a rare earth element called Neodymium which is integral to the glass. This element filters out the yellow hue commonly associated with incandescent lamps. Thus creating a truer and more accurate color of light.



**B10**

### Natural Spectrum

Cand. Base

**S2970** 25 Watt 120V

**S2971** 40 Watt 120V

**S2972** 60 Watt 120V

Packing: 1/Card  
50/Master, 10/Inner



**G16 1/2"**

### Natural Spectrum

Cand. Base

**S2973** 25 Watt 120V

**S2974** 40 Watt 120V

**S2975** 60 Watt 120V

Packing: 1/Card  
50/Master, 10/Inner


Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B10	Cand.	<b>S2970</b>	C32F25VLX	Frosted	120V	2000	220	CC-2V	3 7/8"	1/Card	50/10
25	G16 1/2"	Cand.	<b>S2973</b>	G161/2F25VLX	Frosted	120V	2000	220	CC-2V	3"	1/Card	50/10
40	B10	Cand.	<b>S2971</b>	C32F40VLX	Frosted	120V	2000	370	CC-2V	3 7/8"	1/Card	50/10
40	G16 1/2"	Cand.	<b>S2974</b>	G161/2F40VLX	Frosted	120V	2000	370	CC-2V	3"	1/Card	50/10
60	B10	Cand.	<b>S2972</b>	C32F60VLX	Frosted	120V	2000	650	CC-2V	3 7/8"	1/Card	50/10
60	G16 1/2"	Cand.	<b>S2975</b>	G161/2F60VLX	Frosted	120V	2000	650	CC-2V	3"	1/Card	50/10

specialty lamps

# Natural Spectrum

## Neodymium Lamps 120 Volt / 5000 Hours

*Natural Spectrum Lamps* utilize a rare earth element called Neodymium which is integral to the glass. This element filters out the yellow hue commonly associated with incandescent lamps. Thus creating a truer and more accurate color of light.



R20	R30	R40
<p><b>Flood</b> <b>Natural Spectrum</b> Medium Base <b>S4824</b> 60 Watt Packing: Individually Boxed 50/Master, 10/Inner</p>	<p><b>Flood</b> <b>Natural Spectrum</b> Medium Base <b>S4825</b> 75 Watt <b>S4826</b> 100 Watt Packing: Individually Boxed 50/Master, 10/Inner</p>	<p><b>Flood</b> <b>Natural Spectrum</b> Medium Base <b>S4827</b> 150 Watt Packing: Individually Boxed 50/Master, 10/Inner</p>

**Not Shown Actual Size**

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
60	R20	Med.	S4824	R20FF60VLX	Frosted	120V	5000	520	C-9	4"	Box	50/10
75	R30	Med.	S4825	R30FF75VLX	Frosted	120V	5000	680	C-9	5 3/8"	Box	50/10
100	R30	Med.	S4826	R30FF100VLX	Frosted	120V	5000	1000	C-9	5 3/8"	Box	50/10
150	R40	Med.	S4827	R40FF150VLX	Frosted	120V	5000	1450	C-9	6 1/2"	Box	50/10

# Natural Spectrum

## 120 Volt / 5000 Hours *Neodymium* Lamps



specialty lamps

### A15/A19

**Natural Spectrum**  
Medium Base

- \*\* S2976 40 Watt A15 Frosted
  - S4816 60 Watt A19 Frosted
  - S4817 60 Watt A19 Clear
- Packing: Individually Boxed  
50/Master, 10/Inner

\*\* Carded

### A21

**Natural Spectrum**  
Medium Base

- S4818 75 Watt Frosted
  - S4819 75 Watt Clear
  - S4820 100 Watt Frosted
  - S4821 100 Watt Clear
  - S4822 150 Watt Frosted
- Packing: Individually Boxed  
50/Master, 10/Inner

### 3-Way

**Frosted**  
**Natural Spectrum**

- Medium Base
  - S4823 50/100/150 Watt
- Packing: Individually Boxed  
50/Master, 10/Inner

### G25

**Frosted**  
**Natural Spectrum**

- Medium Base
  - S4815 40 Watt
- Packing: Individually Boxed  
50/Master, 10/Inner

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
40	A15*	Med.	S2976	A15F40VLX	Frosted	120V	5000	300	C-9	3 1/2"	Card/1	50/10
40	G25	Med.	S4815	G25F40VLX	Frosted	120V	5000	320	C-9	4 3/8"	Box	50/10
60	A19	Med.	S4816	A19F60VLX	Frosted	120V	5000	465	C-9	4 1/8"	Box	50/10
60	A19	Med.	S4817	A19C60VLX	Clear	120V	5000	465	C-9	4 1/8"	Box	50/10
75	A21	Med.	S4818	A21F75VLX	Frosted	120V	5000	630	C-9	5 1/16"	Box	50/10
75	A21	Med.	S4819	A21C75VLX	Clear	120V	5000	630	C-9	5 1/16"	Box	50/10
100	A21	Med.	S4820	A21F100VLX	Frosted	120V	5000	910	C-9	5 1/16"	Box	50/10
100	A21	Med.	S4821	A21C100VLX	Clear	120V	5000	910	C-9	5 1/16"	Box	50/10
150	A21	Med.	S4822	A21F150VLX	Frosted	120V	5000	1400	C-9	5 1/16"	Box	50/10
50-150	A21	Med.	S4823	A21F3WVLX	Frosted	120V	5000	350/910/1260	C-9	5 1/16"	Box	50/10

\* Not Shown

## Lamps

Satco Shatter Proof Lamps feature a special mylon® coating which effectively contains glass particles should the lamp break.

These lamps are perfect in food storage preparation, display and sorting tables, hospitals, restaurants and recreation facilities.

Special orders are available for large quantities on specific lamp types.

Not Shown Actual Size



**A15**

**A19**

**A21**

**A21**

**Frosted**  
Medium Base 130V  
**S4880** 25 Watt  
**S4881** 40 Watt  
**S4882** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**Frosted**  
Medium Base 130V  
**S3927** 60 Watt  
**S3928** 75 Watt  
**S3929** 100 Watt  
Packing: Boxed 2 Pack  
24/Master, 12 - 2 Packs  
Sold Per Pack

**Frosted**  
Medium Base 130V  
**S4883** 150 Watt  
Packing: Indiv. Boxed  
24/Master

**Rough Service**  
Medium Base 130V  
**S3972** 75 Watt Frosted  
**S3973** 100 Watt Frosted  
Packing: Indiv. Boxed  
24/Master

Watts	Bulb Type	Base	Satco		Finish	Volts	Avg. Rated		Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
			Order No.	Lamp Code			Hours	Lumens				
25	A15	Med.	<b>S4880</b>	25A15/TF	Frosted	130V	2500	120	C-9	3 1/2"	Box	500/25
40	A15	Med.	<b>S4881</b>	40A15/TF	Frosted	130V	2500	280	C-9	3 1/2"	Box	500/25
60	A15	Med.	<b>S4882</b>	60A15/TF	Frosted	130V	2500	530	C-9	3 1/2"	Box	500/25
60	A19	Med.	<b>S3927</b>	60A19/RS/TF	Frosted	130V	5000	520	C-9	4 1/8"	2/Pks	12
75	A19	Med.	<b>S3928</b>	75A19/RS/TF	Frosted	130V	5000	680	C-9	4 1/8"	2/Pks	12
100	A19	Med.	<b>S3929</b>	100A19/RS/TF	Frosted	130V	5000	960	C-9	4 1/8"	2/Pks	12
75	A21	Med.	<b>S3972</b>	75A21/TF	Frosted	130V	2500	620	C-9	5 5/16"	Box	24
100	A21	Med.	<b>S3973</b>	100A21/TF	Frosted	130V	2500	880	C-9	5 5/16"	Box	24
150	A21	Med.	<b>S4883</b>	150A21/TF	Frosted	130V	2500	1750	C-9	5 5/16"	Box	24



specialty lamps

<i>250R40/HR</i>	<i>250R40/1</i>	<i>BR30</i>	<i>R20</i>
<b>Red Heat Lamp</b> Medium Base 120V <b>S4884</b> 250 Watt Packing: Indiv. Sleeved 12/Master	<b>Clear Heat Lamp</b> Medium Base 120V <b>S4885</b> 250 Watt Packing: Indiv. Sleeved 12/Master	Medium Base 120V <b>S4887</b> 65 Watt Packing: Indiv. Sleeved 96/Master, 12/Inner	Medium Base 120V <b>S4886</b> 50 Watt Packing: Indiv. Sleeved 96/Master, 12/Inner

*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
50	R20	Med.	<b>S4886</b>	50R20/TF	Frost.	120V	2000	375	C-9	4"	Sleeve	96/12
65	BR30	Med.	<b>S4887</b>	65BR30/TF	Frost.	120V	2000	685	C-9	5 3/8"	Sleeve	96/12
250	R40	Med.	<b>S4885</b>	250R40/1/TF	Clear	120V	5000	n/a	C-9	6 7/8"	Sleeve	12
250	R40	Med.	<b>S4884</b>	250R40/HR/TF	Red	120V	5000	n/a	C-9	6 7/8"	Sleeve	12



# Low Voltage *Brass Base*



## Lamps

1500 Hours

Not Shown Actual Size



12 Volt

**Frosted**

Medium Base

- S5010** 25 Watt/A19
- S5011** 50 Watt/A19
- S5012** 75 Watt/A21
- S5013** 100 Watt/A21

Packing: Sleeve, 1 Pack,  
120 Master, 6/Inner



34 Volt

**Frosted**

Medium Base

- S5020** 25 Watt/A19
- S5021** 50 Watt/A19
- S5022** 75 Watt/A21
- S5023** 100 Watt/A21

Packing: Sleeve, 1 Pack,  
120 Master, 6/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	A19	Med.	<b>S5010</b>	25A19/12V	Frost	12V	1500	250	C-6	4 1/8"	Sleeve	120/6
50	A19	Med.	<b>S5011</b>	50A19/12V	Frost	12V	1500	540	C-6	4 1/8"	Sleeve	120/6
75	A21	Med.	<b>S5012</b>	75A21/12V	Frost	12V	1500	720	C-6	5 5/16"	Sleeve	120/6
100	A21	Med.	<b>S5013</b>	100A21/12V	Frost	12V	1500	980	C-6	5 5/16"	Sleeve	120/6
25	A19	Med.	<b>S5020</b>	25A19/34V	Frost	34V	1500	250	C-6	4 1/8"	Sleeve	120/6
50	A19	Med.	<b>S5021</b>	50A19/34V	Frost	34V	1500	540	C-6	4 1/8"	Sleeve	120/6
75	A21	Med.	<b>S5022</b>	75A21/34V	Frost	34V	1500	720	C-6	5 5/16"	Sleeve	120/6
100	A21	Med.	<b>S5023</b>	100A21/34V	Frost	34V	1500	990	C-6	5 5/16"	Sleeve	120/6

specialty lamps

Not Shown Actual Size



**A19/130V**

**A19/230V**

**A19/220V**

**Frosted**  
Euro D.C. Base  
130 Volt  
**S5030** 40 Watt  
**S5031** 60 Watt

**Frosted**  
Euro D.C. Base  
230 Volt  
**S5040** 40 Watt  
**S5041** 60 Watt

**Soft White**  
Medium Base/220 Volt  
**S4076** 40 Watt    **S4078** 75 Watt  
**S4077** 60 Watt    **S4079** 100 Watt  
Packing: Individually Boxed  
120/Master

Packing: Indiv. Boxed  
120/Master

## Halogen - J Type Double Ended



220 Volt  
**S3185** 500 Watt T3Q/CL 118mm  
Packing: Individually Boxed  
12/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
40	A19	Med.	<b>S4076</b>	40A19/F	Frost	220V	2500	330	CC-2F	4 1/8"	Box	120
60	A19	Med.	<b>S4077</b>	60A19/F	Frost	220V	2500	630	CC-2F	4 1/8"	Box	120
75	A19	Med.	<b>S4078</b>	75A19/F	Frost	220V	2500	750	CC-2F	4 1/8"	Box	120
100	A19	Med.	<b>S4079</b>	100A19/F	Frost	220V	2500	1250	CC-2F	4 1/8"	Box	120
40	A19	Euro D.C.	<b>S5030</b>	40A19/F	Frost	130V	2500	330	CC-6	4 1/8"	Box	120
40	A19	Euro D.C.	<b>S5040</b>	40A19/F	Frost	230V	2500	330	CC-2F	4 1/8"	Box	120
60	A19	Euro D.C.	<b>S5031</b>	60A19/F	Frost	130V	2500	630	CC-6	4 1/8"	Box	120
60	A19	Euro D.C.	<b>S5041</b>	60A19/F	Frost	230V	2500	630	CC-2F	4 1/8"	Box	120
500	T3	R7S	<b>S3185</b>	500T3Q/CL	Clear	220V	2000	9500	C-8	4 11/16"	Box	220

220 Volt Brass Base



# Globe Lights G25 3 1/8"

2500 Hours

## Clear

Medium Base  
(220 Volt)

**A3644** 40 Watt

Packing: Individually  
Boxed  
72/Master, 6/Inner



Shown  
Actual Size



## White

Medium Base  
(220 Volt)

**A3645** 40 Watt

Packing: Individually Boxed  
72/Master, 6/Inner



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
40	G25	Med.	<b>A3644</b>	40G25	Clear	220V	2500	212	CC-9	4 3/8"	Box	72/6
40	G25	Med.	<b>A3645</b>	40G25/W	White	220V	2500	187	CC-9	4 3/8"	Box	72/6

# Decorative Torpedo Bulbs

## Bulbs



specialty lamps



**Clear**

E14 Euro Base  
220 Volt  
**S3393** 25 Watt  
**S3394** 40 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



**Clear**

E12 Cand. Base  
220 Volt  
**S3386** 25 Watt  
**S3387** 40 Watt  
**S3388** 60 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



**Frosted**

E12 Cand. Base  
220 Volt  
**S3385** 40 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner



**Clear**

Medium Base  
220 Volt  
**S3384** 40 Watt  
Packing: Indiv. Boxed  
500/Master, 25/Inner

**Bulbs Shown Actual Size**

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B10	E12/Cand.	<b>S3386</b>	25B10	Clear	220V	1000	200	CC-2F	3 3/4"	Box	500/25
25	B10	E14/Euro.	<b>S3393</b>	25B10	Clear	220V	1000	200	CC-2F	3 3/4"	Box	500/25
40	B10	E12/Cand.	<b>S3385</b>	40B10/F	Frost.	220V	1000	330	CC-2F	3 3/4"	Box	500/25
40	B10	E12/Cand.	<b>S3387</b>	40B10	Clear	220V	1000	330	CC-2F	3 3/4"	Box	500/25
40	B10	E14/Euro.	<b>S3394</b>	40B10	Clear	220V	1000	330	CC-2F	3 3/4"	Box	500/25
40	B11	Medium	<b>S3384</b>	40B11	Clear	220V	1000	370	CC-2F	3 7/8"	Box	500/25
60	B10	E12/Cand.	<b>S3388</b>	60B10	Clear	220V	1000	650	CC-2F	3 3/4"	Box	500/25

**230 Volt Brass Base**



# BR38 Weather-Proof Reflectors

Not Shown Actual Size

**2000 Hours**

## BR38 Colors

Medium Base  
230 Volt

- S5002** 100 Watt Red
- S5003** 100 Watt Amber
- S5004** 100 Watt Yellow
- S5005** 100 Watt Green
- S5006** 100 Watt Blue
- S5007** 100 Watt Pink

Packing: Individually Boxed  
6/Master

## BR38 Clear

Medium Base  
230 Volt

- S5000** 75 Watt Flood
- S5001** 150 Watt Flood

Packing: Individually Boxed  
12/Master



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
75	BR38	E27/Med.	<b>S5000</b>	75BR38/FL	Clear	230V	2000	750	CC9	5 5/16"	Box	12
100	BR38	E27/Med.	<b>S5002</b>	100BR38/R	Red	230V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	E27/Med.	<b>S5003</b>	100BR38/A	Amber	230V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	E27/Med.	<b>S5004</b>	100BR38/Y	Yellow	230V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	E27/Med.	<b>S5005</b>	100BR38/G	Green	230V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	E27/Med.	<b>S5006</b>	100BR38/B	Blue	230V	2000	n/a	CC9	5 5/16"	Box	6
100	BR38	E27/Med.	<b>S5007</b>	100BR38/PK	Pink	230V	2000	n/a	CC9	5 5/16"	Box	6
150	BR38	E27/Med.	<b>S5001</b>	150BR38/FL	Clear	230V	2000	1550	CC9	5 5/16"	Box	12

specialty lamps

# Halogen



## PAR16/PAR20/PAR30

*Whiter light, brighter colors, precise beam control.*

Not Shown Actual Size



PAR16

PAR20

PAR30

### SATCO PAR HALOGEN LAMPS QUALITY • VALUE • PERFORMANCE

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
45	PAR16	Med.	S2200	45PAR16/HAL/NFL	NFL 30°	120V	2500	1200	420	CC-8	3 3/16"	Box	15
45	PAR16	Med.	S2300	45PAR16/HAL/NFL	NFL 30°	130V	2500	1200	420	CC-8	3 3/16"	Box	15
60	PAR16	Med.	S2201	60PAR16/HAL/NFL	NFL 30°	120V	2500	1400	600	CC-8	3 3/16"	Box	15
60	PAR16	Med.	S2301	60PAR16/HAL/NFL	NFL 30°	130V	2500	1400	600	CC-8	3 3/16"	Box	15
60	PAR16	Med.	S2202	60PAR16/HAL/NSP	NSP 10°	120V	2500	4700	550	CC-8	3 3/16"	Box	15
60	PAR16	Med.	S2302	60PAR16/HAL/NSP	NSP 10°	130V	2500	4700	550	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S2203	75PAR16/HAL/NFL	NFL 30°	120V	2500	1800	850	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S2303	75PAR16/HAL/NFL	NFL 30°	130V	2500	1800	850	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S2204	75PAR16/HAL/NSP	NSP 10°	120V	2500	7000	850	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S2304	75PAR16/HAL/NSP	NSP 10°	130V	2500	7000	850	CC-8	3 3/16"	Box	15
50	PAR20	Med.	S2205	50PAR20/HAL/NFL	NFL 34°	120V	2500	1300	495	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S2305	50PAR20/HAL/NFL	NFL 34°	130V	2500	1300	495	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S2206	50PAR20/HAL/NSP	NSP 10°	120V	2500	4700	495	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S2306	50PAR20/HAL/NSP	NSP 10°	130V	2500	4700	495	CC-8	3 1/4"	Box	15
50	PAR30	Med.	S2207	50PAR30/HAL/NFL	NFL 34°	120V	2500	1750	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2307	50PAR30/HAL/NFL	NFL 34°	130V	2500	1750	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2208	50PAR30/HAL/WFL	WFL 50°	120V	2500	460	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2308	50PAR30/HAL/WFL	WFL 50°	130V	2500	460	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2209	50PAR30/HAL/NSP	NSP 9°	120V	2500	7600	560	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S2309	50PAR30/HAL/NSP	NSP 9°	130V	2500	7600	56+0	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2210	75PAR30/HAL/NFL	NFL 34°	120V	2500	3100	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2310	75PAR30/HAL/NFL	NFL 34°	130V	2500	3100	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2211	75PAR30/HAL/WFL	WFL 50°	120V	2500	770	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2311	75PAR30/HAL/WFL	WFL 50°	130V	2500	770	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2212	75PAR30/HAL/NSP	NSP 9°	120V	2500	13000	945	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S2312	75PAR30/HAL/NSP	NSP 9°	130V	2500	13000	945	CC-8	3 5/8"	Box	15

halogen lamps

Not Shown Actual Size



PAR38

PAR30LN

### SATCO PAR HALOGEN LAMPS

QUALITY • VALUE • PERFORMANCE

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP*	Lumens	Filament	M.O.L.	Pack Type	Mst. Ctn.
50	PAR30/LN	Med.	<b>S2213</b>	50PAR30/HAL/NFL	NFL 34°	120V	2500	1750	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	<b>S2313</b>	50PAR30/HAL/NFL	NFL 34°	130V	2500	1750	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	<b>S2214</b>	50PAR30/HAL/WFL	WFL 50°	120V	2500	460	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	<b>S2314</b>	50PAR30/HAL/WFL	WFL 50°	130V	2500	460	560	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	<b>S2215</b>	50PAR30/HAL/NSP	NSP 9°	120V	2500	7600	550	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	<b>S2315</b>	50PAR30/HAL/NSP	NSP 9°	130V	2500	7600	550	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	<b>S2216</b>	75PAR30/HAL/NFL	NFL 34°	120V	2500	3100	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	<b>S2316</b>	75PAR30/HAL/NFL	NFL 34°	130V	2500	3100	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	<b>S2217</b>	75PAR30/HAL/WFL	WFL 50°	120V	2500	770	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	<b>S2317</b>	75PAR30/HAL/WFL	WFL 50°	130V	2500	770	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	<b>S2218</b>	75PAR30/HAL/NSP	NSP 9°	120V	2500	13000	945	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	<b>S2318</b>	75PAR30/HAL/NSP	NSP 9°	130V	2500	13000	945	CC-8	4 1/2"	Box	15
45	PAR38	Med.	<b>S2219</b>	45PAR38/HAL/FL	FL 30°	120V	2500	1380	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	<b>S2319</b>	45PAR38/HAL/FL	FL 30°	130V	2500	1380	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	<b>S2220</b>	45PAR38/HAL/NSP	NSP 9°	120V	2500	5000	465	CC-8	5 5/16"	Box	15
45	PAR38	Med.	<b>S2320</b>	45PAR38/HAL/NSP	NSP 9°	130V	2500	5000	465	CC-8	5 5/16"	Box	15
75	PAR38	Med.	<b>S2221</b>	75PAR38/HAL/FL	FL 30°	120V	2500	3200	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	<b>S2321</b>	75PAR38/HAL/FL	FL 30°	130V	2500	3200	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	<b>S2222</b>	75PAR38/HAL/NSP	NSP 9°	120V	2500	16000	960	CC-8	5 5/16"	Box	15
75	PAR38	Med.	<b>S2322</b>	75PAR38/HAL/NSP	NSP 9°	130V	2500	16000	960	CC-8	5 5/16"	Box	15
90	PAR38	Med.	<b>S2223</b>	90PAR38/HAL/FL	FL 30°	120V	2500	3800	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	<b>S2323</b>	90PAR38/HAL/FL	FL 30°	130V	2500	3800	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	<b>S2224</b>	90PAR38/HAL/NSP	NSP 9°	120V	2500	14000	1260	CC-8	5 5/16"	Box	15
90	PAR38	Med.	<b>S2324</b>	90PAR38/HAL/NSP	NSP 9°	130V	2500	14000	1260	CC-8	5 5/16"	Box	15
120	PAR38	Med.	<b>S2225</b>	120PAR38/HAL/FL	FL 30°	120V	2500	4700	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	<b>S2325</b>	120PAR38/HAL/FL	FL 30°	130V	2500	4700	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	<b>S2226</b>	120PAR38/HAL/NSP	NSP 9°	120V	2500	22000	1600	CC-8	5 5/16"	Box	15
120	PAR38	Med.	<b>S2326</b>	120PAR38/HAL/NSP	NSP 9°	130V	2500	22000	1600	CC-8	5 5/16"	Box	15

# Halogen s

## PAR14/PAR16/PAR20

Not Shown Actual Size



PAR14

PAR16

PAR20

Whiter light, brighter colors,  
precise beam control.

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
35	PAR14	Med.	S4658	35PAR14/CAP/WFL	WFL 50°	120V	2000	85	300	CC-8	2 7/16"	Box	6
60	PAR16	Med.	S4900	60PAR16/CAP/NFL	NFL 30°	120V	2000	1300	650	CC-8	2 7/8"	Box	15
60	PAR16	Med.	S4901	60PAR16/CAP/NFL	NFL 30°	130V	2000	1300	650	CC-8	2 7/8"	Box	15
60	PAR16	Med.	S4902	60PAR16/CAP/NSP	NSP 10°	120V	2000	5000	650	CC-8	2 7/8"	Box	15
60	PAR16	Med.	S4903	60PAR16/CAP/NSP	NSP 10°	130V	2000	5000	650	CC-8	2 7/8"	Box	15
75	PAR16	Med.	S4904	75PAR16/CAP/NFL	NFL 30°	120V	2000	1900	900	CC-8	2 7/8"	Box	15
75	PAR16	Med.	S4905	75PAR16/CAP/NFL	NFL 30°	130V	2000	1900	900	CC-8	2 7/8"	Box	15
75	PAR16	Med.	S4906	75PAR16/CAP/NSP	NSP 10°	120V	2000	7500	900	CC-8	2 7/8"	Box	15
75	PAR16	Med.	S4907	75PAR16/CAP/NSP	NSP 10°	130V	2000	7500	900	CC-8	2 7/8"	Box	15
35	PAR20	Med.	S4908	35PAR20/CAP/NFL	NFL 30°	120V	2500	800	360	CC-8	3 1/4"	Box	15
35	PAR20	Med.	S4663	35PAR20/CAP/NFL	NFL 30°	130V	2500	800	360	CC-8	3 1/4"	Box	15
35	PAR20	Med.	S4909	35PAR20/CAP/NSP	NSP 10°	120V	2500	3000	360	CC-8	3 1/4"	Box	15
35	PAR20	Med.	S4661	35PAR20/CAP/NSP	NSP 10°	130V	2500	3000	360	CC-8	3 1/4"	Box	15
35	PAR20	Med.	S4910	35PAR20/CAP/WFL	WFL 40°	120V	2500	500	360	CC-8	3 1/8"	Box	15
35	PAR20	Med.	S4665	35PAR20/CAP/WFL	WFL 40°	130V	2500	500	360	CC-8	3 1/8"	Box	15
50	PAR20	Med.	S4911	50PAR20/CAP/NFL	NFL 30°	120V	2500	1400	550	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S4912	50PAR20/CAP/NFL	NFL 30°	130V	2500	1400	550	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S4913	50PAR20/CAP/NSP	NSP 10°	120V	2500	6200	550	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S4914	50PAR20/CAP/NSP	NSP 10°	130V	2500	6200	550	CC-8	3 1/4"	Box	15
50	PAR20	Med.	S4666	50PAR20/CAP/WFL	WFL 40°	120V	2500	900	550	CC-8	3 1/8"	Box	15



# Halogen **PAR30** Short & Long Neck

Not Shown Actual Size



**PAR30**

Long Neck

**PAR30**

Short Neck

Whiter light, brighter colors, precise beam control.

## SHORT NECK

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP*	Lumens	Filament	M.O.L.	Pack type	Mst. Ctn.
50	PAR30	Med.	<b>S4915</b>	50PAR30/CAP/FL	FL 40°	120V	2500	1300	600	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4916</b>	50PAR30/CAP/FL	FL 40°	130V	2500	1300	600	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4917</b>	50PAR30/CAP/NFL	NFL 25°	120V	2500	2300	660	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4918</b>	50PAR30/CAP/NFL	NFL 25°	130V	2500	2300	660	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4919</b>	50PAR30/CAP/NSP	NSP 9°	120V	2500	8800	660	CC-8	3 5/8"	Box	15
50	PAR30	Med.	<b>S4920</b>	50PAR30/CAP/NSP	NSP 9°	130V	2500	8800	660	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4921</b>	75PAR30/CAP/FL	FL 40°	120V	2500	2000	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4922</b>	75PAR30/CAP/FL	FL 40°	130V	2500	2000	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4923</b>	75PAR30/CAP/NFL	NFL 25°	120V	2500	4000	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4924</b>	75PAR30/CAP/NFL	NFL 25°	130V	2500	4000	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4925</b>	75PAR30/CAP/NSP	NSP 9°	120V	2500	15400	1130	CC-8	3 5/8"	Box	15
75	PAR30	Med.	<b>S4926</b>	75PAR30/CAP/NSP	NSP 9°	130V	2500	15400	1130	CC-8	3 5/8"	Box	15

## LONG NECK

35	PAR30/LN	Med.	<b>S2654</b>	35PAR30LN/CAP/WFL	WFL 50°	120V	2500	450	450	CC-8	4 5/8"	Box	15
35	PAR30/LN	Med.	<b>S2655</b>	35PAR30LN/CAP/NSP	NSP 9°	120V	2500	5700	450	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4927</b>	50PAR30LN/CAP/WFL	WFL 50°	120V	2500	660	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4928</b>	50PAR30LN/CAP/WFL	WFL 50°	130V	2500	660	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4929</b>	50PAR30LN/CAP/NFL	NFL 25°	120V	2500	2300	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4930</b>	50PAR30LN/CAP/NFL	NFL 25°	130V	2500	2300	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4931</b>	50PAR30LN/CAP/NSP	NSP 9°	120V	2500	8800	660	CC-8	4 5/8"	Box	15
50	PAR30/LN	Med.	<b>S4932</b>	50PAR30LN/CAP/NSP	NSP 9°	130V	2500	8800	660	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4933</b>	75PAR30LN/CAP/WFL	WFL 50°	120V	2500	1100	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4934</b>	75PAR30LN/CAP/WFL	WFL 50°	130V	2500	1100	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4935</b>	75PAR30LN/CAP/NFL	NFL 25°	120V	2500	4000	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4936</b>	75PAR30LN/CAP/NFL	NFL 25°	130V	2500	4000	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4937</b>	75PAR30LN/CAP/NSP	NSP 9°	120V	2500	15400	1130	CC-8	4 5/8"	Box	15
75	PAR30/LN	Med.	<b>S4938</b>	75PAR30LN/CAP/NSP	NSP 9°	130V	2500	15400	1130	CC-8	4 5/8"	Box	15

# Halogen

## PAR38



Not Shown Actual Size

Whiter light,  
brighter colors,  
precise beam  
control.



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP*	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
45	PAR38	Med. Skt.	S4939	45PAR/CAP/FL	FL 30°	120V	2500	1500	560	CC-8	5 5/16"	Box	15
45	PAR38	Med. Skt.	S4940	45PAR/CAP/FL	FL 30°	130V	2500	1500	560	CC-8	5 5/16"	Box	15
45	PAR38	Med. Skt.	S4941	45PAR/CAP/NSP	NSP 9°	120V	2500	10000	560	CC-8	5 5/16"	Box	15
45	PAR38	Med. Skt.	S4942	45PAR/CAP/NSP	NSP 9°	130V	2500	10000	560	CC-8	5 5/16"	Box	15
45	PAR38	Med. Skt.	S4630	45PAR/CAP/WFL	WFL 50°	130V	2500	700	560	CC-8	5 5/16"	Box	15
60	PAR38	Med. Skt.	S4943	60PAR/CAP/FL	FL 30°	120V	3000	2500	850	CC-8	5 5/16"	Box	15
60	PAR38	Med. Skt.	S4944	60PAR/CAP/FL	FL 30°	130V	3000	2500	850	CC-8	5 5/16"	Box	15
60	PAR38	Med. Skt.	S4945	60PAR/CAP/NSP	NSP 9°	120V	3000	16000	850	CC-8	5 5/16"	Box	15
60	PAR38	Med. Skt.	S4946	60PAR/CAP/NSP	NSP 9°	130V	3000	16000	850	CC-8	5 5/16"	Box	15
75	PAR38	Med. Skt.	S4964	75PAR/CAP/FL	FL 30°	120V	2500	3150	1060	CC-8	5 5/16"	Box	15
75	PAR38	Med. Skt.	S4965	75PAR/CAP/FL	FL 30°	130V	2500	3150	1060	CC-8	5 5/16"	Box	15
75	PAR38	Med. Skt.	S4966	75PAR/CAP/NSP	NSP 9°	120V	2500	19200	1060	CC-8	5 5/16"	Box	15
75	PAR38	Med. Skt.	S4967	75PAR/CAP/NSP	NSP 9°	130V	2500	19200	1060	CC-8	5 5/16"	Box	15
75	PAR38	Med. Skt.	S4631	75PAR/CAP/WFL	WFL 50°	130V	2500	1300	1060	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4968	90PAR/CAP/FL	FL 30°	120V	2500	3500	1310	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4969	90PAR/CAP/FL	FL 30°	130V	2500	3500	1310	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4970	90PAR/CAP/NSP	NSP 9°	120V	2500	19000	1310	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4971	90PAR/CAP/NSP	NSP 9°	130V	2500	19000	1310	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4950	90PAR/CAP/WSP	WSP 12°	120V	2500	14300	1310	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4951	90PAR/CAP/WSP	WSP 12°	130V	2500	14300	1310	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4632	90PAR/CAP/NFL	NFL 25°	130V	2500	4700	1310	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4633	90PAR/CAP/WFL	WFL 50°	130V	2500	1600	1310	CC-8	5 5/16"	Box	15
120	PAR38	Med. Skt.	S4972	120PAR/CAP/FL	FL 30°	120V	3000	4600	1800	CC-8	5 5/16"	Box	15
120	PAR38	Med. Skt.	S4973	120PAR/CAP/FL	FL 30°	130V	3000	4600	1800	CC-8	5 5/16"	Box	15
120	PAR38	Med. Skt.	S4974	120PAR/CAP/SP	SP 10°	120V	3000	22500	1800	CC-8	5 5/16"	Box	15
120	PAR38	Med. Skt.	S4975	120PAR/CAP/SP	SP 10°	130V	3000	22500	1800	CC-8	5 5/16"	Box	15
120	PAR38	Med. Skt.	S4634	120PAR/CAP/WFL	WFL 50°	130V	3000	2000	1800	CC-8	5 5/16"	Box	15
250	PAR38	Med. Skt.	S4947	250PAR/CAP/FL	FL 30°	120V	4500	4500	3600	CC-8	5 5/16"	Box	6
250	PAR38	Med. Skt.	S4948	250PAR/CAP/SP	SP 10°	120V	4500	46500	3600	CC-8	5 5/16"	Box	6

halogen lamps

# SATCO® SOFTRAY™ PAR Reflectors

Not Shown Actual Size

## PAR16/PAR20/PAR30/PAR38



### Frosted Halogen Lamps

#### S O F T - R A Y

Introducing – Soft Ray , a new concept in halogen lighting. Our new line of frosted MR16 and PAR lamps offer a simple, cost effective solution to problems normally associated with standard halogen reflectors.

It is known that many users of traditional MR16 & PAR lamps object to the “headlamp look” or glary appearance of these lamps. Soft Ray lamps solve these problems and more!

- Glare Free
- Does not create hot spots
- Eliminates shadows & striations
- Produces a smooth and even beam pattern



PAR16



PAR20



PAR30 Short Neck



PAR30 Long Neck



PAR38

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
60	PAR16	Med.	S4108	60PAR16/FL/FROST	Flood 38°	120V	2500	525	CC-8	3 3/16"	Box	15
75	PAR16	Med.	S4109	75PAR16/FL/FROST	Flood 38°	120V	2500	725	CC-8	3 3/16"	Box	15
50	PAR20	Med.	S4100	50PAR20/NFL/FROST	Flood 38°	120V	2500	450	CC-8	3 3/8"	Box	15
50	PAR20	Med.	S4200	50PAR20/NFL/FROST	Flood 38°	130V	2500	450	CC-8	3 3/8"	Box	15
50	PAR30	Med.	S4101	50PAR30/FL/FROST	Flood 38°	120V	2500	520	CC-8	3 5/8"	Box	15
50	PAR30	Med.	S4201	50PAR30/FL/FROST	Flood 38°	130V	2500	520	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S4102	75PAR30/FL/FROST	Flood 38°	120V	2500	900	CC-8	3 5/8"	Box	15
75	PAR30	Med.	S4202	75PAR30/FL/FROST	Flood 38°	130V	2500	900	CC-8	3 5/8"	Box	15
50	PAR30/LN	Med.	S4103	50PAR30/LN/FL/FROST	Flood 38°	120V	2500	520	CC-8	4 1/2"	Box	15
50	PAR30/LN	Med.	S4203	50PAR30/LN/FL/FROST	Flood 38°	130V	2500	520	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S4104	75PAR30/LN/FL/FROST	Flood 38°	120V	2500	900	CC-8	4 1/2"	Box	15
75	PAR30/LN	Med.	S4204	75PAR30/LN/FL/FROST	Flood 38°	130V	2500	900	CC-8	4 1/2"	Box	15
45	PAR38	Med. Skt.	S4105	45PAR38/FL/FROST	Flood 38°	120V	2500	450	CC-8	5 5/16"	Box	15
45	PAR38	Med. Skt.	S4205	45PAR38/FL/FROST	Flood 38°	130V	2500	450	CC-8	5 5/16"	Box	15
60	PAR38	Med. Skt.	S4106	60PAR38/FL/FROST	Flood 38°	120V	2500	600	CC-8	5 5/16"	Box	15
60	PAR38	Med. Skt.	S4206	60PAR38/FL/FROST	Flood 38°	130V	2500	600	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4107	90PAR38/FL/FROST	Flood 38°	120V	2500	1150	CC-8	5 5/16"	Box	15
90	PAR38	Med. Skt.	S4207	90PAR38/FL/FROST	Flood 38°	130V	2500	1150	CC-8	5 5/16"	Box	15

halogen lamps

# Halogen Reflectors



## R20/BR30 & BR40

2500 Hours

- Nickel Plated Brass Base
- High Lumen Output
- Brilliant White Light
- Better Color Rendering than Standard Floods
- 20% Brighter & Longer Lasting



halogen lamps

R20	BR30	BR40
Medium Base 120 Volt <b>S4500</b> 50 Watt Packing: Individually Sleeved 48/Master, 6/Inner	Medium Base 120 Volt/130Volt <b>S4501</b> 60 Watt <b>S4401</b> 60 Watt/130 Volt <b>S4502</b> 75 Watt <b>S4402</b> 75 Watt/130 Volt Packing: Individually Sleeved 48/Master, 6/Inner	Medium Base 120 Volt <b>S4504</b> 75 Watt <b>S4503</b> 100 Watt Packing: Individually Sleeved 24/Master, 6/Inner

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Lumens	Kelvin	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
50	R20	Med.	<b>S4500</b>	50R20/FL/HAL	70°	120V	2500	480	3000K	4"	Sleeve	6/48
60	BR30	Med.	<b>S4501</b>	60BR30/FL/HAL	80°	120V	2500	730	3000K	5 3/8"	Sleeve	6/48
60	BR30	Med.	<b>S4401</b>	60BR30/FL/HAL	80°	130V	2500	730	3000K	5 3/8"	Sleeve	6/48
75	BR30	Med.	<b>S4502</b>	75BR30/FL/HAL	80°	120V	2500	900	3000K	5 3/8"	Sleeve	6/48
75	BR30	Med.	<b>S4402</b>	75BR30/FL/HAL	80°	130V	2500	900	3000K	5 3/8"	Sleeve	6/48
75	BR40	Med.	<b>S4504</b>	75BR40/FL/HAL	90°	120V	2500	900	3000K	6 1/2"	Sleeve	6/24
100	BR40	Med.	<b>S4503</b>	100BR40/FL/HAL	90°	120V	2500	1400	3000K	6 1/2"	Sleeve	6/24

All lamps rated at design voltage.

## 2000 Hours / 12 & 24 Volt **MR8 & MR11** Lamps

Not Shown  
Actual Size

### MR8 Lensed

12 Volt  
**S4646** 10W NSP  
**S4645** 10W NFL  
Packing: Individually Boxed,  
12/Cartron



### MR11 Bayonet / Lensed

12 Volt  
**S1954** 20W SP FST/C  
**S1952** 20W NFL FSV/C  
**S1955** 35W SP GDY/C  
**S1953** 35W NFL GDZ/C  
Packing: Individually Boxed  
12/Cartron



### MR11 12 Volt

**S3194** 5W NSP  
**S3195** 10W SP  
**S3150** 20W NSP FTB  
**S3152** 20W SP FTC  
**S3154** 20W NFL FTD  
**S3151** 35W NSP FTE  
**S3153** 35W SP FTF  
**S3155** 35W NFL FTH

Packing: Individually Boxed,  
12/Cartron



### MR11 Frosted GZ4 / Lensed

12 Volt  
**S4124** 20W FL  
**S4125** 35W FL  
Packing: Individually Boxed  
12/Cartron



### MR11 Lensed

12 Volt  
**S1950** 20W NFL FTD/C  
**S1951** 35W NFL FTH/C  
24 Volt  
**S1990** 20W NSP FTD/C  
**S1988** 20W NFL FTD/C  
**S1991** 35W NSP FTH/C  
**S1989** 35W NFL FTH/C  
Packing: Individually Boxed,  
12/Cartron



Watts	Bulb Type	Base	Satco Order No.	ANSI Code	Lamp Code	Beam	Volts	Avg. Rated Hours	Candle Power	Filament	M.O.L.	Pack. Type	Mst. Ctn.
10	MR8	GZ4	<b>S4646</b>	n/a	10MR8/NSP	SP9°	12V	2000	tbd	C-6	1 1/4"	Box	12
10	MR8	GZ4	<b>S4645</b>	n/a	10MR8/NFL	NFL23°	12V	2000	tbd	C-6	1 1/4"	Box	12
5	MR11	GZ4	<b>S3194</b>	n/a	5MR11/NSP	NSP9°	12V	2000	tbd	C-6	1 1/4"	Box	12
10	MR11	GZ4	<b>S3195</b>	n/a	10MR11/SP	SP12°	12V	2000	tbd	C-6	1 1/4"	Box	12
20	MR11	GZ4	<b>S3150</b>	FTB	20MR11/NSP	NSP9°	12V	2000	4100	C-6	1 1/4"	Box	12
20	MR11	GZ4	<b>S1990</b>	FIB/C/24	20MR11/NSP/C	NSP9°	24V	2000	4100	C-6	1 1/4"	Box	12
20	MR11	GZ4	<b>S3152</b>	FTC	20MR11/SP	SP12°	12V	2000	1750	C-6	1 1/4"	Box	12
20	MR11	DC.Bay	<b>S1954</b>	FST/C	20MR11/DC/SP/C	SP12°	12V	2000	1750	C-6	1 5/8"	Box	12
20	MR11	GZ4	<b>S3154</b>	FTD	20MR11/NFL	NFL24°	12V	2000	700	C-6	1 1/4"	Box	12
20	MR11	GZ4	<b>S1950</b>	FTD/C	20MR11/NFL/C	NFL24°	12V	2000	700	C-6	1 1/4"	Box	12
20	MR11	GZ4	<b>S1988</b>	FTD/C/24	20MR11/NFL/C	NFL24°	24V	2000	700	C-6	1 1/4"	Box	12
20	MR11	DC.Bay	<b>S1952</b>	FSV/C	20MR11/DC/NFL/C	NFL24°	12V	2000	700	C-6	1 5/8"	Box	12
20	MR11	GZ4	<b>S4124</b>	n/a	20MR11/FL/FR	FL36°	12V	2000	288	C-6	1 1/4"	Box	12
35	MR11	GZ4	<b>S3151</b>	FTE	35MR11/NSP	NSP9°	12V	2000	7000	C-6	1 1/4"	Box	12
35	MR11	GZ4	<b>S1991</b>	FIE/C/24	35MR11/NSP/C	NSP9°	24V	2000	tbd	C-6	1 1/4"	Box	12
35	MR11	GZ4	<b>S3153</b>	FTF	35MR11/SP	SP12°	12V	2000	1500	C-6	1 1/4"	Box	12
35	MR11	DC.Bay	<b>S1955</b>	GDY/C	35MR11/DC/SP/C	SP12°	12V	2000	1500	C-6	1 5/8"	Box	12
35	MR11	GZ4	<b>S3155</b>	FTH	35MR11/NFL	NFL24°	12V	2000	700	C-6	1 1/4"	Box	12
35	MR11	GZ4	<b>S1951</b>	FTH/C	35MR11/NFL/C	NFL24°	12V	2000	700	C-6	1 1/4"	Box	12
35	MR11	GZ4	<b>S1989</b>	FTH/C/24	35MR11/C	NFL24°	24V	2000	1500	C-6	1 1/4"	Box	12
35	MR11	DC.Bay	<b>S1953</b>	GDZ/C	35MR11/DC/NFL/C	NFL24°	12V	2000	700	C-6	1 5/8"	Box	12
35	MR11	GZ4	<b>S4125</b>	n/a	35MR11/FL/FR	FL36°	12V	2000	520	C-6	1 1/4"	Box	12

# Halogen

## MR16 Lamps 120V



2000 Hours

halogen lamps



**JDR Lensed**  
120 Volt/Medium  
**S3139** 50W Flood  
**S3113** 75W Flood  
**S3114** 100W Flood  
120 Volt/Intermediate  
**S3115** 75W Flood  
**S3116** 100W Flood  
Packing: Individually Boxed  
12/Carton



**MR16 Lensed/Short**  
120 Volt/Med. Base  
**S4623** 20W FL BAB/C  
**S4624** 35W FL FMW/C  
**S4625** 50W FL EXN/C  
Packing: Individually Boxed  
12/Carton



**MR16 Lensed Standard Pin**  
120 Volt/GX5.3 Base  
**S1976** 20W FL BAB/C  
**S1977** 35W FL FMW/C  
**S1978** 50W FL EXN/C  
Packing: Individually Boxed  
12/Carton



**MR16 Lensed Wide Pin**  
120 Volt/G8 Base  
**S4626** 20W FL BAB/C  
**S4627** 35W FL FMW/C  
**S4618** 50W FL EXN/C  
Packing: Individually Boxed  
12/Carton



**MR16 Lensed Twist Lock**  
120 Volt/GU10 Base  
**S3515** 20W Flood  
**S3516** 35W Flood  
**S3517** 50W Flood  
Packing: 12 Cards/Inner  
120 Cards/Master



**MR16 Lensed Twist Lock / Frosted**  
120 Volt/GU10 Base  
**S4127** 20W Flood  
**S4128** 35W Flood  
**S4129** 50W Flood  
Packing: Individually Boxed  
12/Carton

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Candle Power	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
20	MR16	GX5.3	<b>S1976</b>	20MR16/FL/C	FL 36°	120V	2000	700	CC-8	1 7/8"	Box	12
20	MR16	G8	<b>S4618</b>	20MR16/G8/FL/C	FL 36°	120V	2000	700	CC-8	1 7/8"	Box	12
20	MR16	GU10	<b>S3515</b>	20MR16/GU10/FL	FL 36°	120V	2000	700	CC-8	1 7/8"	Box	12
20	MR16	GU10	<b>S4127</b>	20MR16/GU10/Frost	FL 36°	120V	2000	650	CC-8	1 7/8"	Box	12
20	MR16	Med.	<b>S4623</b>	20MR16/S/FL/C	FL 36°	120V	2000	700	CC-8	1 3/4"	Box	12
35	MR16	GX5.3	<b>S1977</b>	35MR16/FL/C	FL 36°	120V	2000	1250	CC-8	1 7/8"	Box	12
35	MR16	G8	<b>S4626</b>	35MR16/G8/FL/C	FL 36°	120V	2000	1250	CC-8	1 7/8"	Box	12
35	MR16	GU10	<b>S3516</b>	35MR16/GU10/FL	FL 36°	120V	2000	1250	CC-8	1 7/8"	Box	12
35	MR16	GU10	<b>S4128</b>	35MR16/GU10/Frost	FL 36°	120V	2000	1200	CC-8	1 7/8"	Box	12
35	MR16	Med.	<b>S4624</b>	35MR16/S/FL/C	FL 36°	120V	2000	1250	CC-8	1 3/4"	Box	12
50	MR16	GX5.3	<b>S1978</b>	50MR16/FL/C	FL 36°	120V	2000	1700	CC-8	1 7/8"	Box	12
50	MR16	G8	<b>S4627</b>	50MR16/G8/FL/C	FL 36°	120V	2000	1700	CC-8	1 7/8"	Box	12
50	MR16	GU10	<b>S3517</b>	50MR16/GU10/FL	FL 36°	120V	2000	1700	CC-8	1 7/8"	Box	12
50	MR16	GU10	<b>S4129</b>	50MR16/GU10/Frost	FL 36°	120V	2000	1650	CC-8	1 7/8"	Box	12
50	MR16	Med.	<b>S4625</b>	50MR16/S/FL/C	FL 36°	120V	2000	1700	CC-8	1 3/4"	Box	12
50	JDR	Med.	<b>S3139</b>	50JDR16/FL	FL 36°	120V	2000	1500	CC-8	2 7/8"	Box	12
75	JDR	Int.	<b>S3115</b>	75JDR16/N/FL	FL 36°	120V	2000	1650	CC-8	2 7/8"	Box	12
75	JDR	Med.	<b>S3113</b>	75JDR16/FL	FL 36°	120V	2000	1650	CC-8	2 7/8"	Box	12
100	JDR	Int.	<b>S3116</b>	100JDR16/N/FL	FL 36°	120V	2000	1950	CC-8	2 7/8"	Box	12
100	JDR	Med.	<b>S3114</b>	100JDR16/FL	FL 36°	120V	2000	1950	CC-8	2 7/8"	Box	12

2000 Hours / 12 Volt

# MR16 Lamps



### MR16 12 Volt

<b>S1956</b> 20W FL BAB	<b>S1962</b> 50W MFL EXZ
<b>S1957</b> 20W NSP ESX	<b>S1963</b> 50W VWFL FNV
<b>S1958</b> 35W NSP FRB	<b>S1964</b> 65W FL FPB
<b>S1959</b> 35W FL FMW	<b>S1965</b> 65W NSP FPA
<b>S1960</b> 50W FL EXN	Packing: Individually Boxed
<b>S1961</b> 50W NSP EXT	12/Carton

### Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	ANSI	Lamp Code	Beam	Volts	Avg. Rated Hours	Candle Power	Filament	M.O.L.	Pack. Type	Mst. Ctn.
20	MR16	GX5.3	<b>S1957</b>	ESX	20MR16/NSP	NSP 9°	12V	2000	4100	C-8	1 7/8"	Box	12
20	MR16	GX5.3	<b>S1956</b>	BAB	20MR16/FL	FL 36°	12V	2000	700	C-6	1 7/8"	Box	12
35	MR16	GX5.3	<b>S1958</b>	FRB	35MR16/NSP	NSP 9°	12V	2000	7000	C-6	1 7/8"	Box	12
35	MR16	GX5.3	<b>S1959</b>	FMW	35MR16/FL	FL 36°	12V	2000	1250	C-6	1 7/8"	Box	12
50	MR16	GX5.3	<b>S1961</b>	EXT	50MR16/NSP	NSP 9°	12V	2000	10000	C-6	1 7/8"	Box	12
50	MR16	GX5.3	<b>S1962</b>	EXZ	50MR16/NFL	NFL 18°	12V	2000	4400	C-6	1 7/8"	Box	12
50	MR16	GX5.3	<b>S1960</b>	EXN	50MR16/FL	FL 36°	12V	2000	1700	C-8	1 7/8"	Box	12
50	MR16	GX5.3	<b>S1963</b>	FNV	50MR16/WFL	VWFL 60°	12V	2000	2200	C-6	1 7/8"	Box	12
65	MR16	GX5.3	<b>S1965</b>	FPA	65MR16/NSP	NSP 9°	12V	2000	9530	C-6	1 7/8"	Box	12
65	MR16	GX5.3	<b>S1964</b>	FPB	65MR16 FPB	FL 36°	12V	2000	3600	C-6	1 7/8"	Box	12

halogen lamps

# Halogen MR16 Lamps



2000 Hours / 12 & 24 Volt

## MR16 Bayonet / Lensed 12 Volt

- S1970 20W FL GES/C
- S1971 20W NSP GEV/C
- S1972 50W FL GBW/C
- S1973 50W NSP GBT/C
- S1974 65W FL FPB/C
- S1975 65W NSP FPA/C

Packing: Individually Boxed  
12/Cartron



## MR16 Lensed 24 Volt

- S1992 20W FL
- S1993 35W FL
- S1994 50W FL
- S1995 20W SP
- S1996 35W SP
- S1997 50W SP

Packing: Individually Boxed  
12/Cartron



## MR16 Lensed 12 Volt

- S1966 20W FL BAB/C
- S1967 20W NSP ESX/C
- S4365 35W FL FMW/C
- S4364 35W NSP FRB/C
- S3169 50W FL EXN/C
- S3170 50W NSP EXT/C
- S1968 65W FL FPB/C
- S1969 65W NSP FPA/C

Packing: Individually Boxed  
20/Cartron



## MR16 Frosted Lensed 12 Volt

- S4120 20W FL BAB/C
- S4121 35W FL FMW/C
- S4122 50W FL EXN/C
- S4123 65W FL FPB/C

Packing: Individually Boxed,  
12/Cartron



Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Candle Power	Filament	M.O.L.	Pack. Type	Mst.Ctn./Inner Pack
20	MR16	GX5.3	S1966	20MR16/FL/C	FL 36°	12V	2000	700	C-8	1 7/8"	Box	12
20	MR16	GX5.3	S4120	20MR16/FL/FROST/C	FL 36°	12V	2000	288	C-6	1 7/8"	Box	12
20	MR16	D.C.Bay.	S1970	20MR16/FL/DC/C	FL 36°	12V	2000	700	C-6	1 7/8"	Box	12
20	MR16	GX5.3	S1992	20MR16/FL/C	FL 36°	24V	2000	700	C-8	1 7/8"	Box	12
20	MR16	GX5.3	S1967	20MR16/NSP/C	NSP 9°	12V	2000	4100	C-8	1 7/8"	Box	12
20	MR16	D.C.Bay.	S1971	20MR16/NSP/DC/C	NSP 9°	12V	2000	4100	C-8	1 7/8"	Box	12
20	MR16	GX5.3	S1995	20MR16/NSP/C	NSP 9°	24V	2000	4100	C-8	1 7/8"	Box	12
35	MR16	GX5.3	S4365	35MR16/FL/C	FL 36°	12V	2000	1250	C-8	1 7/8"	Box	12
35	MR16	GX5.3	S1993	35MR16/FL/C	FL 36°	24V	2000	700	C-8	1 7/8"	Box	12
35	MR16	GX5.3	S4121	35MR16/FL/FROST	FL 36°	12V	2000	520	C-6	1 7/8"	Box	12
35	MR16	GX5.3	S4364	35MR16/NSP/C	NSP 9°	12V	2000	7000	C-8	1 7/8"	Box	12
35	MR16	GX5.3	S1996	35MR16/NSP/C	NSP 9°	24V	2000	7000	C-6	1 7/8"	Box	12
50	MR16	GX5.3	S3169	50MR16/FL/C	FL 36°	12V	2000	1700	C-8	1 7/8"	Box	12
50	MR16	GX5.3	S4122	50MR16/FL/FROST	FL 36°	12V	2000	820	C-6	1 7/8"	Box	12
50	MR16	D.C.Bay.	S1972	50MR16/FL/DC/C	FL 36°	12V	2000	1700	C-8	1 7/8"	Box	12
50	MR16	GX5.3	S1994	50MR16/FL	FL 36°	24V	2000	1700	C-8	1 7/8"	Box	12
50	MR16	GX5.3	S3170	50MR16/NSP/C	NSP 9°	12V	2000	10000	C-8	1 7/8"	Box	12
50	MR16	D.C.Bay.	S1973	50MR16/NSP/DC/C	NSP 9°	12V	2000	10000	C-8	1 7/8"	Box	12
50	MR16	GX5.3	S1997	50MR16/NSP/C	NSP 9°	24V	2000	10000	C-8	1 7/8"	Box	12
65	MR16	GX5.3	S1968	65MR16/FL/C	FL 36°	12V	2000	3600	C-8	1 7/8"	Box	12
65	MR16	GX5.3	S4123	65MR16/FL/FROST/C	FL 36°	12V	2000	880	C-6	1 7/8"	Box	12
65	MR16	D.C.Bay.	S1974	65MR16/FL/DC/C	FL 36°	12V	2000	tbd	C-6	1 7/8"	Box	12
65	MR16	GX5.3	S1969	65MR16/NSP/C	NSP 9°	12V	2000	9500	C-8	1 7/8"	Box	12
65	MR16	D.C.Bay.	S1975	65MR16/NSP/DC/C	NSP 9°	12V	2000	9500	C-8	1 7/8"	Box	12

halogen lamps



# Halogen

4000 Hours

Not Shown Actual Size

# MR16 Specialty Lamps



**Aluminized Reflector**

- Projects Heat & Light out the front of the lamp
- Minimizes the "Backlight Effect"
- Constant Color Technology



**Hard Coated Dichroic Reflector**

- Projects Heat out the back of the lamp
- Constant Color Technology



**Energy Saving**

- Hard Coated Dichroic Reflector
- Infra-Red Reflective Coating
- Constant Color Technology
- Lensed

Watts	Bulb Type	Base	Satco Order No.	ANSI	Lamp Code	Volts	Avg. Rated Hours	Candle Power	Filament	M.O.L.	Pack. Type	Mst. Ctn
<b>Aluminized Reflector</b>												
20	MR16	GU5.3	<b>S2601</b>	BAB	20MR16/B/FL35	12V	4000	625	AX	1 3/4"	Box	10
20	MR16	GU5.3	<b>S2602</b>	BAB/C	20MR16/B/FL35/C	12V	4000	600	AX	1 3/4"	Box	10
20	MR16	GU5.3	<b>S2603</b>	ESX	20MR16/B/NSP8	12V	4000	4650	AX	1 3/4"	Box	10
20	MR16	GU5.3	<b>S2604</b>	ESX/C	20MR16/B/NSP8/C	12V	4000	4400	AX	1 3/4"	Box	10
35	MR16	GU5.3	<b>S2605</b>	FMW	35MR16/B/FL35	12V	4000	1300	AX	1 3/4"	Box	10
35	MR16	GU5.3	<b>S2606</b>	FRB	35MR16/B/NSP10	12V	4000	8700	AX	1 3/4"	Box	10
50	MR16	GU5.3	<b>S2607</b>	EXN	50MR16/B/FL35	12V	4000	1900	AX	1 3/4"	Box	10
50	MR16	GU5.3	<b>S2608</b>	EXN/C	50MR16/B/FL35/C	12V	4000	1800	AX	1 3/4"	Box	10
50	MR16	GU5.3	<b>S2609</b>	EXZ	50MR16/B/NFL25	12V	4000	3000	AX	1 3/4"	Box	10
50	MR16	GU5.3	<b>S2610</b>	EXT	50MR16/B/NSP11	12V	4000	10500	AX	1 3/4"	Box	10
50	MR16	GU5.3	<b>S2611</b>	EXT/C	50MR16/B/NSP11/C	12V	4000	10000	AX	1 3/4"	Box	10
65	MR16	GU5.3	<b>S2612</b>	FPB	65MR16/B/FL40	12V	4000	2100	AX	1 3/4"	Box	10
65	MR16	GU5.3	<b>S2613</b>	FPC	65MR16/B/NFL25	12V	4000	3600	AX	1 3/4"	Box	10
65	MR16	GU5.3	<b>S2614</b>	FPA	65MR16/B/NSP10	12V	4000	12500	AX	1 3/4"	Box	10
<b>Hard Coated Dichroic Reflector</b>												
20	MR16	GU5.3	<b>S2615</b>	BAB	20MR16/T/FL40	12V	4000	700	AX	1 3/4"	Box	20
20	MR16	GU5.3	<b>S2616</b>	ESX	20MR16/T/NSP10	12V	4000	5000	AX	1 3/4"	Box	20
20	MR16	GU5.3	<b>S2617</b>	n/a	20MR16/T/WFL60	12V	4000	350	AX	1 3/4"	Box	20
35	MR16	GU5.3	<b>S2618</b>	FMW	35MR16/T/FL40	12V	4000	1250	AX	1 3/4"	Box	20
35	MR16	GU5.3	<b>S2619</b>	n/a	35MR16/T/NFL25	12V	4000	3100	AX	1 3/4"	Box	20
35	MR16	GU5.3	<b>S2620</b>	FRB	35MR16/T/NSP10	12V	4000	8300	AX	1 3/4"	Box	20
35	MR16	GU5.3	<b>S2621</b>	n/a	35MR16/T/WFL60	12V	4000	650	AX	1 3/4"	Box	20
50	MR16	GU5.3	<b>S2622</b>	EXN	50MR16/T/FL40	12V	4000	2000	AX	1 3/4"	Box	20
50	MR16	GU5.3	<b>S2623</b>	EXZ	50MR16/T/NFL25	12V	4000	3200	AX	1 3/4"	Box	20
50	MR16	GU5.3	<b>S2624</b>	EXT	50MR16/T/NSP10	12V	4000	11500	AX	1 3/4"	Box	20
50	MR16	GU5.3	<b>S2625</b>	FNV	50MR16/T/WFL60	12V	4000	1000	AX	1 3/4"	Box	20
65	MR16	GU5.3	<b>S2626</b>	FPB	65MR16/T/FL40	12V	4000	2100	AX	1 3/4"	Box	20
65	MR16	GU5.3	<b>S2627</b>	FPC	65MR16/T/NFL25	12V	4000	4000	AX	1 3/4"	Box	20
65	MR16	GU5.3	<b>S2628</b>	FPA	65MR16/T/NSP10	12V	4000	14000	AX	1 3/4"	Box	20
65	MR16	GU5.3	<b>S2629</b>	n/a	65MR16/T/WFL60	12V	4000	1050	AX	1 3/4"	Box	20
<b>Infra-Red Reflecting Energy Saver</b>												
20	MR16	GU5.3	<b>S2630</b>	n/a	20MR16/IR/FL40/C	12V	4000	1000	AX	1 3/4"	Box	20
20	MR16	GU5.3	<b>S2631</b>	n/a	20MR16/IR/NFL25/C	12V	4000	2300	AX	1 3/4"	Box	20
20	MR16	GU5.3	<b>S2632</b>	n/a	20MR16/IR/NSP10/C	12V	4000	6000	AX	1 3/4"	Box	20
20	MR16	GU5.3	<b>S2633</b>	n/a	20MR16/IR/WFL60/C	12V	4000	450	AX	1 3/4"	Box	20
37	MR16	GU5.3	<b>S2634</b>	n/a	37MR16/IR/FL40/C	12V	4000	2200	AX	1 3/4"	Box	20
37	MR16	GU5.3	<b>S2635</b>	n/a	37MR16/IR/NFL25/C	12V	4000	4400	AX	1 3/4"	Box	20
37	MR16	GU5.3	<b>S2636</b>	n/a	37MR16/IR/NSP10/C	12V	4000	12500	AX	1 3/4"	Box	20
37	MR16	GU5.3	<b>S2637</b>	n/a	37MR16/IR/WFL60/C	12V	4000	1100	AX	1 3/4"	Box	20
50	MR16	GU5.3	<b>S2638</b>	n/a	50MR16/IR/FL40/C	12V	4000	2850	AX	1 3/4"	Box	20
50	MR16	GU5.3	<b>S2639</b>	n/a	50MR16/IR/NFL25/C	12V	4000	5700	AX	1 3/4"	Box	20
50	MR16	GU5.3	<b>S2640</b>	n/a	50MR16/IR/NSP10/C	12V	4000	15000	AX	1 3/4"	Box	20
50	MR16	GU5.3	<b>S2641</b>	n/a	50MR16/IR/WFL60/C	12V	4000	1430	AX	1 3/4"	Box	20

halogen lamps

# Closed Aluminum

## Reflector (ALR) Lamps

2000 Hours/12 Volt

halogen lamps



**37mm ALR**  
**D.C. Bayonet**

12 Volt

**S2642** 20W Narrow Spot GBD

Packing: Individually Boxed  
Master/50, Inner/5



**37mm ALR**  
**D.C. Bayonet**

12 Volt

**S2643** 20W Spot GBE  
**S2644** 20W Flood GBF

Packing: Individually Boxed  
Master/50, Inner/5



**56mm ALR**  
**D.C. Bayonet**

12 Volt

**S2645** 50W Flood GBK

Packing: Individually Boxed  
Master/50, Inner/5



**56mm ALR**  
**D.C. Bayonet**

12 Volt

**S2646** 50W Spot GBJ

Packing: Individually Boxed  
Master/50, Inner/5

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Candle Power	Kelvin	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
20	37mm ALR	D.C. Bay	<b>S2642</b>	20ALR12/NSP6-GBD	6°	12V	2000	6400	3000K	1 3/8"	Box	50/5
20	37mm ALR	D.C. Bay	<b>S2643</b>	20ALR12/SP18-GBE	18°	12V	2000	1000	3000K	1 3/8"	Box	50/5
20	37mm ALR	D.C. Bay	<b>S2644</b>	20ALR12/FL34-GBF	34°	12V	2000	350	3000K	1 3/8"	Box	50/5
50	56mm ALR	D.C. Bay	<b>S2646</b>	50ALR18/SP10-GBJ	10°	12V	2000	12,000	3000K	2 1/2"	Box	50/5
50	56mm ALR	D.C. Bay	<b>S2645</b>	50ALR18/NFL22-GBK	22°	12V	2000	2000	3000K	2 1/2"	Box	50/5

# Halogen Aluminum Reflectors **AR70 & AR111**

**3000 Hours**

UV stop capsule with axial filament in precisely engineered aluminum reflector.



**AR111**



**AR70**

## Screw Terminal Base

<b>S4685</b> 35 Watt Super Spot	<b>S4692</b> 75 Watt Flood
<b>S4686</b> 35 Watt Spot	<b>S4693</b> 75 Watt Wide Flood
<b>S4687</b> 35 Watt Flood	<b>S4694</b> 100 Watt Spot
<b>S4688</b> 50 Watt Super Spot	<b>S4695</b> 100 Watt Flood
<b>S4689</b> 50 Watt Spot	<b>S4696</b> 100 Watt Wide Flood
<b>S4690</b> 50 Watt Flood	Packing: Individually Boxed
<b>S4691</b> 75 Watt Spot	6/Master

## D.C. Bayonet Base

<b>S4680</b> 20 Watt Spot
<b>S4681</b> 20 Watt Flood
<b>S4682</b> 50 Watt Spot
<b>S4683</b> 50 Watt Flood
Packing: Individually Boxed
10/Master

## Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP*	Filament	M.O.L.	Pack. Type	Mst. Ctn.
20	AR70	DC Bayonet	<b>S4680</b>	20AR70/SP8	Spot 8°	12V	3000	7700	C-8	1 15/16"	Box	10
20	AR70	DC Bayonet	<b>S4681</b>	20AR70/FL25	Flood 25°	12V	3000	900	C-8	1 15/16"	Box	10
50	AR70	DC Bayonet	<b>S4682</b>	50AR70/SP8	Spot 8°	12V	3000	12500	C-8	1 15/16"	Box	10
50	AR70	DC Bayonet	<b>S4683</b>	50AR70/FL25	Flood 25°	12V	3000	2600	C-8	1 15/16"	Box	10
35	AR111	G53	<b>S4684</b>	35AR111/SSP4	Super Spot 4°	12V	3000	40000	C-8	2 3/8"	Box	6
35	AR111	G53	<b>S4686</b>	35AR111/SP8	Spot 8°	12V	3000	14000	C-8	2 5/16"	Box	6
35	AR111	G53	<b>S4687</b>	35AR111/FL25	Flood 25°	12V	3000	2500	C-8	2 5/16"	Box	6
50	AR111	G53	<b>S4688</b>	50AR111/SSP4	Super Spot 4°	12V	3000	45000	C-8	2 3/8"	Box	6
50	AR111	G53	<b>S4689</b>	50AR111/SP8	Spot 8°	12V	3000	20000	C-8	2 1/4"	Box	6
50	AR111	G53	<b>S4690</b>	50AR111/FL25	Flood 25°	12V	3000	4000	C-8	2 5/16"	Box	6
75	AR111	G53	<b>S4691</b>	75AR111/SP8	Spot 8°	12V	3000	30000	C-8	2 1/4"	Box	6
75	AR111	G53	<b>S4692</b>	75AR111/FL25	Flood 25°	12V	3000	5300	C-8	2 5/16"	Box	6
75	AR111	G53	<b>S4693</b>	75AR111/WFL45	Wide Flood 45°	12V	3000	2000	C-8	2 3/8"	Box	6
100	AR111	G53	<b>S4694</b>	100AR111/SP8	Spot 8°	12V	3000	48000	C-8	2 1/4"	Box	6
100	AR111	G53	<b>S4695</b>	100AR111/FL25	Flood 25°	12V	3000	8500	C-8	2 5/16"	Box	6
100	AR111	G53	<b>S4696</b>	100AR111/WFL45	Wide Flood 45°	12V	3000	2800	C-8	2 3/8"	Box	6

halogen lamps



# Halogen Sealed Beam Reflectors **PAR36/PAR56/PAR64**

halogen lamps



**PAR36**  
**Screw Terminal**

**PAR56**  
**Mogul End Prong**

**PAR64**  
**Mogul End Prong**

**2 Piece Construction**  
12 Volt

**2 Piece Construction**  
120 Volt

**2 Piece Construction**  
120 Volt

- S4807** 36 Watt Very Narrow Spot
- S4808** 36 Watt Narrow Spot
- S4809** 36 Watt Wide Flood
- S4806** 50 Watt Narrow Spot

Packing: Individually Boxed  
12/Master

- S4669** 500 Watt Med. Flood
- S4668** 500 Watt Narrow Spot
- S4670** 500 Watt Wide Flood

Packing: Individually Boxed  
12/Master

- S4672** 1000 Watt Med. Flood
- S4671** 1000 Watt Narrow Spot
- S4673** 1000 Watt Wide Flood

Packing: Individually Boxed  
6/Master

### Not Shown Actual Size

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP*	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
36	PAR36	Screw Term.	<b>S4807</b>	36PAR36/CAP/VNSP	Spot 5°	12V	4000	17000	500	C-8	2 3/4"	Box	12
36	PAR36	Screw Term.	<b>S4808</b>	36PAR36/CAP/NSP	Spot 13°	12V	4000	3500	500	C-8	2 3/4"	Box	12
36	PAR36	Screw Term.	<b>S4809</b>	36PAR36/CAP/WFL	Flood 32°	12V	4000	1000	500	C-8	2 3/4"	Box	12
50	PAR36	Screw Term.	<b>S4806</b>	50PAR36/CAP/NSP6	Spot 6°	12V	4000	25000	700	C-8	2 3/4"	Box	12
500	PAR56	Mogul End Prong	<b>S4668</b>	500PAR56Q/NSP	Narrow Spot 15°	120V	4000	78500	8800	CC-6	5"	Box	12
500	PAR56	Mogul End Prong	<b>S4669</b>	500PAR56Q/MFL	Med. Flood 30°	120V	4000	40000	8800	CC-6	5"	Box	12
500	PAR56	Mogul End Prong	<b>S4670</b>	500PAR56Q/WFL	Wide Flood 45°	120V	4000	19500	8800	CC-6	5"	Box	12
1000	PAR64	Mogul End Prong	<b>S4671</b>	1000PAR64Q/NSP	Narrow Spot 20°	120V	4000	135000	19400	CC-6	6"	Box	6
1000	PAR64	Mogul End Prong	<b>S4672</b>	1000PAR64Q/MFL	Med. Flood 30°	120V	4000	82000	19400	CC-6	6"	Box	6
1000	PAR64	Mogul End Prong	<b>S4673</b>	1000PAR64Q/WFL	Wide Flood 60°	120V	4000	23000	19400	CC-6	6"	Box	6

# Halogen General Service Lamps



**3 Way Reading Light Soft White**  
**Medium Base/120 Volt**  
**S4505** 30/70/100 Watt  
**S4506** 50/100/150 Watt  
 Packing: 1/Sleeve  
 12/Inner  
 36/Master

Dual halogen capsules create 3 light levels



**A-Type**  
**Medium Base/120 Volt**

- S4600** 60 Watt White
- S4601** 75 Watt White
- S4602** 100 Watt White
- S4603** 60 Watt Clear
- S4604** 150 Watt White
- Packing: 6/Inner  
 6/Inner - Tray Pack  
 60/Master

**Not Shown Actual Size**



**Double-Envelope JDD Type**  
**Medium Base/120 Volt**

- S3472** 75 Watt Clear
- S3476** 75 Watt Frosted
- S3473** 100 Watt Clear
- S3477** 100 Watt Frosted
- S3474** 150 Watt Clear
- S3478** 150 Watt Frosted
- S3475** 250 Watt Clear
- S3479** 250 Watt Frosted

Packing: 1 Bulb/Card  
 12 Cards/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
60	BT15	Med.	<b>S4603</b>	60BT15/CL	Clear	120V	5000	700	CC-8	4"	Card/1	60/6
60	BT15	Med.	<b>S4600</b>	60BT15/W	White	120V	5000	600	CC-8	4"	Card/1	60/6
75	BT15	Med.	<b>S4601</b>	75BT15/W	White	120V	5000	800	CC-8	4"	Card/1	60/6
75	T10	Med.	<b>S3472</b>	75T10Q/CL	Clear	120V	2000	1050	CC-8	4"	Card/1	12
75	T10	Med.	<b>S3476</b>	75T10Q/F	Frosted	120V	2000	1000	CC-8	4"	Card/1	12
100	BT15	Med.	<b>S4602</b>	100BT15/W	White	120V	5000	1200	CC-8	4"	Card/1	60/6
100	T10	Med.	<b>S3473</b>	100T10Q/CL	Clear	120V	2000	1500	CC-8	4"	Card/1	12
100	T10	Med.	<b>S3477</b>	100T10Q/F	Frosted	120V	2000	1420	CC-8	4"	Card/1	12
150	BT15	Med.	<b>S4604</b>	150BT15/W	White	120V	5000	1600	CC-8	4"	Card/1	60/6
150	T10	Med.	<b>S3474</b>	150T10Q/CL	Clear	120V	2000	2500	CC-8	4"	Card/1	12
150	T10	Med.	<b>S3478</b>	150T10Q/F	Frosted	120V	2000	2300	CC-8	4"	Card/1	12
250	T10	Med.	<b>S3475</b>	250T10Q/CL	Clear	120V	2000	4200	CC-8	4"	Card/1	12
250	T10	Med.	<b>S3479</b>	250T10Q/F	Frosted	120V	2000	3900	CC-8	4"	Card/1	12

**3-Way Reading Light**

30								295	CC-8			
70	A21	E26/Med.	<b>S4505</b>	30/70/100A21/W	White	120V	4000	785	CC-8	5 1/16"	Sleeve	36/12
100								1080				
50								585	CC-8			
100	A21	E26/Med.	<b>S4506</b>	50/100/150A21/W	White	120V	4000	1400	CC-8	5 1/16"	Sleeve	36/12
150								1985				

halogen lamps

# Halogen



## JD Bayonet Lamps

2000 Hours

### JD Bayonet

120 Volt

- S1979** 35 Watt
- S1981** 50 Watt
- S3159** 75 Watt
- S3147** 100 Watt
- S3122** 150 Watt
- S3123** 250 Watt
- S1983** 500 Watt

Packing:  
Individually Boxed  
12/Carton



### JD Frosted Bayonet

120 Volt

- S1980** 35 Watt
- S1982** 50 Watt
- S1919** 75 Watt
- S1920** 100 Watt
- S1921** 150 Watt
- S1922** 250 Watt
- S1984** 500 Watt

Packing:  
Individually Boxed  
12/Carton



Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
35	T4	DC. Bay	<b>S1979</b>	35Q/CL	Clear	120V	2000	400	CC-8	2 23/32"	Box	12
35	T4	DC. Bay	<b>S1980</b>	35Q/F	Frost	120V	2000	360	CC-8	2 23/32"	Box	12
50	T4	DC. Bay	<b>S1981</b>	50Q/CL	Clear	120V	2000	750	CC-8	2 23/32"	Box	12
50	T4	DC. Bay	<b>S1982</b>	50Q/F	Frost	120V	2000	675	CC-8	2 23/32"	Box	12
75	T4	DC. Bay	<b>S3159</b>	75Q/CL	Clear	120V	2000	1250	CC-8	2 13/32"	Box	12
75	T4	DC. Bay	<b>S1919</b>	75Q/F	Frost	120V	2000	1125	CC-8	2 13/32"	Box	12
100	T4	DC. Bay	<b>S3147</b>	100Q/CL	Clear	120V	2000	1600	CC-8	2 13/32"	Box	12
100	T4	DC. Bay	<b>S1920</b>	100Q/F	Frost	120V	2000	1440	CC-8	2 13/32"	Box	12
150	T4.5	DC. Bay	<b>S3122</b>	150Q/CL	Clear	120V	2000	2400	CC-8	2 13/32"	Box	12
150	T4.5	DC. Bay	<b>S1921</b>	150Q/F	Frost	120V	2000	2160	CC-8	2 13/32"	Box	12
250	T4.5	DC. Bay	<b>S3123</b>	250Q/CL	Clear	120V	2000	4350	CC-8	2 27/32"	Box	12
250	T4.5	DC. Bay	<b>S1922</b>	250Q/F	Frost	120V	2000	3915	CC-8	2 27/32"	Box	12
500	T4.5	DC. Bay	<b>S1983</b>	500Q/CL	Clear	120V	2000	8500	CC-8	3 3/4"	Box	12
500	T4.5	DC. Bay	<b>S1984</b>	500Q/F	Frost	120V	2000	7650	CC-8	3 3/4"	Box	12

halogen lamps

2000 Hours



**JD**

**Clear Mini Can**

120 Volt

- S3165** 35 Watt
- S3162** 50 Watt
- S3157** 75 Watt
- S3107** 100 Watt
- S3108** 150 Watt
- S3109** 250 Watt
- S3181** 500 Watt

130 Volt

- S3198** 50 Watt

Packing: Individually Boxed  
12/Carton



**JD**

**Frosted Mini Can**

120 Volt

- S1913** 35 Watt
- S1914** 50 Watt
- S1915** 75 Watt
- S1916** 100 Watt
- S1917** 150 Watt
- S1918** 250 Watt
- S3182** 500 Watt

Packing:

Individually Boxed  
12/Carton



**JD E-14**

**European**

120 Volt

- S3132** 100 Watt
- S3133** 150 Watt
- S3134** 250 Watt

Packing:  
Individually Boxed  
12/Carton

**Not Shown  
Actual Size**

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
35	T4	E11	<b>S3165</b>	35Q/CL	Clear	120V	2000	400	CC-8	2 5/16"	Box	12
35	T4	E11	<b>S1913</b>	35Q/F	Frost	120V	2000	360	CC-8	2 5/16"	Box	12
50	T4	E11	<b>S3162</b>	50Q/CL	Clear	120V	2000	750	CC-8	2 5/16"	Box	12
50	T4	E11	<b>S1914</b>	50Q/F	Frost	120V	2000	675	CC-8	2 5/16"	Box	12
50	T4	E11	<b>S3198</b>	50Q/CL	Clear	130V	2000	750	CC-8	2 5/16"	Box	12
75	T4	E11	<b>S3157</b>	75Q/CL	Clear	120V	2000	1250	CC-8	2 11/16"	Box	12
75	T4	E11	<b>S1915</b>	75Q/F	Frost	120V	2000	1125	CC-8	2 11/16"	Box	12
100	T4	E11	<b>S3107</b>	100Q/CL	Clear	120V	2000	1600	CC-8	2 11/16"	Box	12
100	T4	E11	<b>S1916</b>	100Q/F	Frost	120V	2000	1440	CC-8	2 11/16"	Box	12
100	T4.5	E14	<b>S3132</b>	100Q/CL	Clear	120V	2000	1600	CC-8	2 15/16"	Box	12
150	T4.5	E11	<b>S3108</b>	150Q/CL	Clear	120V	2000	2400	CC-8	2 23/32"	Box	12
150	T4.5	E11	<b>S1917</b>	150Q/F	Frost	120V	2000	2160	CC-8	2 23/32"	Box	12
150	T4.5	E14	<b>S3133</b>	150Q/CL	Clear	120V	2000	2400	CC-8	3 1/32"	Box	12
250	T4.5	E11	<b>S3109</b>	250Q/CL	Clear	120V	2000	4350	CC-8	3 5/32"	Box	12
250	T4.5	E11	<b>S1918</b>	250Q/F	Frost	120V	2000	3915	CC-8	3 5/32"	Box	12
250	T4.5	E14	<b>S3134</b>	250Q/CL	Clear	120V	2000	4350	CC-8	3 11/32"	Box	12
500	T4.5	E11	<b>S3181</b>	500Q/CL	Clear	120V	2000	8500	CC-8	3 15/32"	Box	12
500	T4.5	E11	<b>S3182</b>	500Q/F	Frost	120V	2000	7650	CC-8	3 15/32"	Box	12

halogen lamps

# Krypton/Xenon

## High Performance Lamps

3000 Hours  
120 Volt



**Frosted**  
E-11  
Mini Can Base  
S4489 20 Watt  
S4490 40 Watt  
S4491 60 Watt



**Frosted**  
D.C.  
Bayonet Base  
S4495 20 Watt  
S4496 40 Watt  
S4497 60 Watt



**Clear**  
D.C.  
Bayonet Base  
S4492 20 Watt  
S4493 40 Watt  
S4494 60 Watt



**Clear**  
E-11  
Mini Can Base  
S4486 20 Watt  
S4487 40 Watt  
S4488 60 Watt



**Frosted**  
E-12  
Candelabra Base  
S4483 20 Watt  
S4484 40 Watt  
S4485 60 Watt



**Clear**  
E-12  
Candelabra Base  
S4480 20 Watt  
S4481 40 Watt  
S4482 60 Watt

White light similar to halogen • Less heat • Lamps can be touched  
Fully dimmable • No Significant UV.

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
20	T3	E12	S4480	KX20CL/E12	Clear	120V	3000	200	CC-8	2 7/16"	Box	100/10
20	T3	E12	S4483	KX20FR/E12	Frost.	120V	3000	200	CC-8	2 7/16"	Box	100/10
20	T3	E11	S4486	KX20CL/E11	Clear	120V	3000	200	CC-8	2 5/16"	Box	100/10
20	T3	E11	S4489	KX20FR/E11	Frost	120V	3000	200	CC-8	2 5/16"	Box	100/10
20	T3	D.C. Bay	S4492	KX20CL/DC	Clear	120V	3000	200	CC-8	2 1/4"	Box	100/10
20	T3	D.C. Bay	S4495	KX20FR/DC	Frost	120V	3000	200	CC-8	2 1/4"	Box	100/10
40	T3	E12	S4481	KX40CL/E12	Clear	120V	3000	560	CC-8	2 7/16"	Box	100/10
40	T3	E12	S4484	KX40FR/E12	Frost	120V	3000	560	CC-8	2 7/16"	Box	100/10
40	T3	E11	S4487	KX40CL/E11	Clear	120V	3000	560	CC-8	2 5/16"	Box	100/10
40	T3	E11	S4490	KX40FR/E11	Frost	120V	3000	560	CC-8	2 5/16"	Box	100/10
40	T3	D.C. Bay	S4493	KX40CL/DC	Clear	120V	3000	560	CC-8	2 1/4"	Box	100/10
40	T3	D.C. Bay	S4496	KX40FR/DC	Frost	120V	3000	560	CC-8	2 1/4"	Box	100/10
60	T3	E12	S4482	KX60CL/E12	Clear	120V	3000	960	CC-8	2 7/16"	Box	100/10
60	T3	E12	S4485	KX60FR/E12	Frost	120V	3000	960	CC-8	2 7/16"	Box	100/10
60	T3	E11	S4488	KX60CL/E11	Clear	120V	3000	960	CC-8	2 5/16"	Box	100/10
60	T3	E11	S4491	KX60FR/E11	Frost	120V	3000	960	CC-8	2 5/16"	Box	100/10
60	T3	D.C. Bay	S4494	KX60CL/DC	Clear	120V	3000	960	CC-8	2 1/4"	Box	100/10
60	T3	D.C. Bay	S4497	KX60FR/DC	Frost	120V	3000	960	CC-8	2 1/4"	Box	100/10



## Bi-Pin Lamps

2000 Hours



**Frosted Bi Pin**

**12 Volt**

- S1908** 10 Watt
- S1909** 20 Watt
- S1910** 35 Watt
- S1911** 50 Watt
- S1912** 75 Watt

Packing:  
Individually Boxed  
48/Cartron



**Bi Pin**

**12 Volt**

- S3179** 5 Watt
- S3171** 10 Watt
- S3120** 20 Watt
- S3160** 35 Watt
- S3121** 50 Watt
- S3156** 75 Watt

**24 Volt**

- S1986** 20 Watt
  - S1987** 50 Watt
- Packing: Individually  
Boxed, 48/Cartron



**Bi Pin**

**120 Volt  
GY6.35 Base**

- S3197** 25 Watt
- S3164** 35 Watt
- S3167** 50 Watt
- S3168** 75 Watt
- S1924** 100 Watt

Packing:  
Individually Boxed  
48/Cartron



**Bi Pin**

**120 Volt (Wide Pin)  
G8 Base**

- S4610** 20 Watt
- S4611** 25 Watt
- S4620** 35 Watt
- S4612** 50 Watt
- S4613** 75 Watt
- S4622** 100 Watt

Packing:  
Individually Boxed  
48/Cartron



**Double Loop**

**120 Volt  
G9 Base**

- S4614** 20 Watt
- S4615** 25 Watt
- S4621** 35 Watt
- S4616** 50 Watt
- S4617** 75 Watt
- S4642** 100 Watt

Packing:  
Individually Boxed  
48/Cartron

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
5	T3	G4.	<b>S3179</b>	5T3	Clear	12V	2000	50	C-6	32 MM	Box	48
10	T3	G4.	<b>S3171</b>	10T3	Clear	12V	2000	120	C-6	32 MM	Box	48
10	T3	G4	<b>S1908</b>	10T3/F	Frost	12V	2000	100	C-6	32 MM	Box	48
20	T3	G4	<b>S3120</b>	20T3	Clear	12V	2000	320	C-6	32 MM	Box	48
20	T3	G4	<b>S1909</b>	20T3/F	Frost	12V	2000	300	C-6	32 MM	Box	48
20	T3	G4	<b>S1986</b>	20T3	Clear	24V	2000	260	C-6	32 MM	Box	48
20	T4	G8	<b>S4610</b>	20T4	Clear	120V	2000	180	C-6	46 MM	Box	48
20	T4	G9	<b>S4614</b>	20T4	Clear	120V	2000	180	C-6	45 MM	Box	48
25	T4	G8	<b>S4611</b>	25T4/F	Clear	120V	2000	240	C-6	46 MM	Box	48
25	T4	GY6.35	<b>S3197</b>	25T4	Clear	120V	2000	240	CC-8	50 MM	Box	48
25	T4	G9	<b>S4615</b>	25T4/F	Clear	120V	2000	240	C-6	45 MM	Box	48
35	T4	GY6.35	<b>S3160</b>	35T4	Clear	12V	2000	600	C-6	41 MM	Box	48
35	T4	GY6.35	<b>S1910</b>	35T4/F	Frost	12V	2000	550	C-6	41 MM	Box	48
35	T4	GY6.35	<b>S3164</b>	35T4	Clear	120V	2000	400	CC-8	50 MM	Box	48
35	T4	G8	<b>S4620</b>	35T4	Clear	120V	2000	400	C-6	46 MM	Box	48
35	T4	G9	<b>S4621</b>	35T4	Clear	120V	2000	400	C-6	45 MM	Box	48
50	T4	G8	<b>S4612</b>	50T4	Clear	120V	2000	750	C-6	46 MM	Box	48
50	T4	GY6.35	<b>S3121</b>	50T4	Clear	12V	2000	900	C-6	41 MM	Box	48
50	T4	GY6.35	<b>S1911</b>	50T4/F	Frost	12V	2000	850	C-6	41 MM	Box	48
50	T4	GY6.35	<b>S1987</b>	50T4	Clear	24V	2000	850	C-6	41 MM	Box	48
50	T4	GY6.35	<b>S3167</b>	50T4	Clear	120V	2000	750	CC-8	50 MM	Box	48
50	T4	G9	<b>S4616</b>	50T4	Clear	120V	2000	750	C-6	45 MM	Box	48
75	T4	GY6.35	<b>S3156</b>	75T4	Clear	12V	2000	1350	C-6	41 MM	Box	48
75	T4	GY6.35	<b>S1912</b>	75T4/F	Frost	12V	2000	1290	C-6	41 MM	Box	48
75	T4	GY6.35	<b>S3168</b>	75T4	Clear	120V	2000	1250	CC-8	60 MM	Box	48
75	T4	G8	<b>S4613</b>	75T4/F	Clear	120V	2000	1250	C-6	58 MM	Box	48
75	T4	G9	<b>S4617</b>	75T4/F	Clear	120V	2000	1250	C-6	56 MM	Box	48
100	T4	GY6.35	<b>S1924</b>	100T4	Clear	120V	2000	2000	CC-8	60 MM	Box	48
100	T4	G8	<b>S4622</b>	100T4/F	Clear	120V	2000	2000	CC-8	58 MM	Box	48

## Double Ended Lamps

2000 Hours




**78MM J-Type (Short)**

120 Volt	130 Volt
<b>S3199</b> 75 Watt	<b>S3183</b> 75 Watt
<b>S3146</b> 100 Watt	Packing:
<b>S3135</b> 150 Watt	Individually Boxed,
<b>S3145</b> 200 Watt	12/Master
<b>S3184</b> 250 Watt	



**118MM J-Type (Long)**

120 Volt	130 Volt
<b>S3166</b> 100 Watt	<b>S1925</b> 300 Watt
<b>S3142</b> 150 Watt	<b>S1926</b> 500 Watt
<b>S3136</b> 200 Watt	Packing:
<b>S3104</b> 300 Watt	Individually Boxed,
<b>S3105</b> 500 Watt	12/Master



**254MM J-Type (Long)**

240 Volt

**S3106** 1500 Watt

Packing: Individually Boxed,  
12/Master

**Flat Blade**



**145MM J-Type (Blade)**

120 Volt

**S3180** 300 Watt

**S1923** 500 Watt

Packing: Individually Boxed,  
12/Master


**Not Shown Actual Size**

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
75	T3	R7S	<b>S3199</b>	75T3Q/CL	Clear	120V	2000	1200	C-8	3 1/8"	Box	12
75	T3	R7S	<b>S3183</b>	75T3Q/CL	Clear	130V	2000	1200	C-8	3 1/8"	Box	12
100	T3	R7S	<b>S3146</b>	100T3Q/CL	Clear	120V	2000	1650	C-8	3 1/8"	Box	12
100	T3	R7S	<b>S3166</b>	100T3Q/CL	Clear	120V	2000	1650	C-8	4 11/16"	Box	12
150	T3	R7S	<b>S3135</b>	150T3Q/CL	Clear	120V	2000	2600	C-8	3 1/8"	Box	12
150	T3	R7S	<b>S3142</b>	150T3Q/CL	Clear	120V	2000	2600	C-8	4 11/16"	Box	12
200	T3	R7S	<b>S3145</b>	200T3Q/CL	Clear	120V	2000	3200	C-8	3 1/8"	Box	12
200	T3	R7S	<b>S3136</b>	200T3Q/CL	Clear	120V	2000	3200	C-8	4 11/16"	Box	12
250	T3	R7S	<b>S3184</b>	250T3Q/CL	Clear	120V	2000	3950	C-8	3 1/8"	Box	12
300	T3	R7S	<b>S3104</b>	300T3Q/CL	Clear	120V	2000	5000	C-8	4 11/16"	Box	12
300	T3	R7S	<b>S1925</b>	300T3Q/CL	Clear	130V	2000	5000	C-8	4 11/16"	Box	12
300	T3	Blade	<b>S3180</b>	300T3Q/CL	Clear	120V	2000	5000	C-8	5 13/16"	Box	12
500	T3	R7S	<b>S3105</b>	500T3Q/CL	Clear	120V	2000	9500	C-8	4 11/16"	Box	12
500	T3	R7S	<b>S1926</b>	500T3Q/CL	Clear	130V	2000	9500	C-8	4 11/16"	Box	12
500	T3	Blade	<b>S1923</b>	500T3Q/CL	Clear	120V	2000	9500	C-8	5 13/16"	Box	12
1500	T3	R7S	<b>S3106</b>	1500T3Q/CL	Clear	240V	2000	33000	C-8	10 1/16"	Box	12


halogen lamps

2000 Hours


Application Suggestions




Miniature Pendant Fixtures




Vanity Lighting



Cable Systems



Landscape Lighting



Decorative Fixtures



**JCGV-14.4**

12 Volt  
1.8" Diameter  
**S3187** 20W  
**S3188** 35W  
**S3189** 50W  
Packing:  
Individually Boxed  
200/Master, 25/Inner



**JCGV-12.8**

12 Volt  
1.6" Diameter  
**S3193** 20W  
Packing:  
Individually Boxed  
200/Master, 25/Inner

U.L. classified  
for U.V. filtration  
and particle  
containment



**JCGV-14.4**  
**Long Neck**

12 Volt  
1.8" Diameter  
**S3190** 20W  
**S3191** 35W  
**S3192** 50W  
Packing:  
Individually Boxed  
200/Master, 25/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
20	GV14.4	GX5.3	<b>S3187</b>	20JVG2-614	White	12V	2000	320	C-6	2.22"	Box	200/25
35	GV14.4	GX5.3	<b>S3188</b>	35JVG2-614	White	12V	2000	620	C-6	2.22"	Box	200/25
50	GV14.4	GX5.3	<b>S3189</b>	50JVG2-614	White	12V	2000	940	C-6	2.22"	Box	200/25
20	GV14.4	GX5.3	<b>S3190</b>	20JVG2L-614	White	12V	2000	320	C-6	2.57"	Box	200/25
35	GV14.4	GX5.3	<b>S3191</b>	35JVG2L-614	White	12V	2000	620	C-6	2.57"	Box	200/25
50	GV14.4	GX5.3	<b>S3192</b>	50JVG2L-614	White	12V	2000	940	C-6	2.57"	Box	200/25
20	GV12.8	G4	<b>S3193</b>	20JVG2L-614	White	12V	2000	340	C-6	2.22"	Box	200/25

halogen lamps

# Halogen A-Type Lamps



**Post Light**

**S2647** 50 Watt  
**S1942** 75 Watt  
 Packing:  
 Individually Boxed  
 12/Master

Unique faceted bulb provides brilliant white halogen light for decorative outdoor fixtures.



**A-Type**

**S1943** 42 Watt  
**S2648** 42 Watt 130V  
**S1944** 52 Watt  
**S2649** 52 Watt 130V  
**S1946** 60 Watt  
**S1945** 72 Watt  
**S2650** 72 Watt 130V  
**S1947** 75 Watt  
**S1948** 100 Watt

Packing:  
 Individually Boxed  
 12/Master

*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
42	A19	Medium	<b>S1943</b>	42A/CAP	Frost	120V	3500	570	CC-8	4 3/8"	Box	12
42	A19	Medium	<b>S2648</b>	42A/CAP/130	Frost	130V	3500	570	CC-8	4 3/8"	Box	12
50	A19	Medium	<b>S2647</b>	50A/HAL/CRYSTAL	Crystal	120V	2500	860	CC-8	4 3/8"	Box	12
52	A19	Medium	<b>S1944</b>	52A/CAP	Frost	120V	3500	770	CC-8	4 3/8"	Box	12
52	A19	Medium	<b>S2649</b>	52A/CAP/130	Frost	130V	3500	770	CC-8	4 3/8"	Box	12
60	A19	Medium	<b>S1946</b>	60A/HAL	Frost	120V	3000	960	CC-8	4 3/8"	Box	12
72	A19	Medium	<b>S1945</b>	72A/CAP	Frost	120V	3500	1150	CC-8	4 3/8"	Box	12
72	A19	Medium	<b>S2650</b>	72A/CAP/130	Frost	130V	3500	1150	CC-8	4 3/8"	Box	12
75	A19	Medium	<b>S1942</b>	75A/HAL/CRYSTAL	Crystal	120V	3000	1330	CC-8	4 3/8"	Box	12
75	A19	Medium	<b>S1947</b>	75A/HAL	Frost	120V	3000	1300	CC-8	4 3/8"	Box	12
100	A19	Medium	<b>S1948</b>	100A/HAL	Frost	120V	3000	1800	CC-8	4 3/8"	Box	12
<b>130 volt Specifications on 120 Volt Line</b>												
37	A19	Medium	<b>S2648</b>	42A/CAP/130	Frost	130V	7000	450	CC-8	4 3/8"	Box	12
46	A19	Medium	<b>S2649</b>	52A/CAP/130	Frost	130V	7000	600	CC-8	4 3/8"	Box	12
63	A19	Medium	<b>S2650</b>	72A/CAP/130	Frost	130V	7000	900	CC-8	4 3/8"	Box	12

# Turn-Tip *Candelabra Base*



## Carded Bulbs

1500 Hours / 120 Volt

carded lamps



**Clear**

**S3773** 15 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Clear**

**S3774** 25 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Clear**

**S3762** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Clear**

**S3775** 40 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	CA-8	Cand.	<b>S3773</b>	15CA8	Clear	120V	1500	100	C-7A	3 5/8"	Card/2	120/10
25	CA-8	Cand.	<b>S3774</b>	25CA8	Clear	120V	1500	210	CC-2V	3 5/8"	Card/2	120/10
40	CA-9 1/2	Cand.	<b>S3775</b>	40CA9 1/2	Clear	120V	1500	370	CC-2V	3 15/16"	Card/2	120/10
60	CA-10	Cand.	<b>S3762</b>	60CA10	Clear	120V	1500	672	CC-2V	4 1/4"	Card/2	120/10

**1500 Hours / 120 Volt**

**Frosted**  
**S3777** 15 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Frosted**  
**S3778** 25 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Frosted**  
**S3779** 40 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Frosted**  
**S3763** 60 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	CA-8	Cand.	<b>S3777</b>	15CA8/F	Frosted	120V	1500	90	C-7A	3 5/8"	Card/2	120/10
25	CA-8	Cand.	<b>S3778</b>	25CA8/F	Frosted	120V	1500	200	CC-2V	3 5/8"	Card/2	120/10
40	CA-9 1/2	Cand.	<b>S3779</b>	40CA9 1/2/F	Frosted	120V	1500	350	CC-2V	3 15/16"	Card/2	120/10
60	CA-10	Cand.	<b>S3763</b>	60CA10/F	Frosted	120V	1500	635	CC-2V	4 1/4"	Card/2	120/10

Carded lamps

# Torpedo *Candelabra Base*



## Carded Bulbs

1500 Hours / 120 Volt

### Clear

**S3782** 25 Watt

**S3783** 40 Watt

**S3784** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



### Frosted

**S3785** 25 Watt

**S3786** 40 Watt

**S3787** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



Not Shown Actual Size

### White

**S3788** 25 Watt

**S3789** 40 Watt

**S3790** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B9 1/2	Cand.	<b>S3782</b>	25B9 1/2	Clear	120V	1500	212	CC-2V	3 1/2"	Card/2	120/10
25	B9 1/2	Cand.	<b>S3785</b>	25B9 1/2/F	Frosted	120V	1500	212	CC-2V	3 1/2"	Card/2	120/10
25	B9 1/2	Cand.	<b>S3788</b>	25B9 1/2/W	White	120V	1500	180	CC-2V	3 1/2"	Card/2	120/10
40	B9 1/2	Cand.	<b>S3783</b>	40B9 1/2	Clear	120V	1500	384	CC-2V	3 1/2"	Card/2	120/10
40	B9 1/2	Cand.	<b>S3786</b>	40B9 1/2/F	Frosted	120V	1500	384	CC-2V	3 1/2"	Card/2	120/10
40	B9 1/2	Cand.	<b>S3789</b>	40B9 1/2/W	White	120V	1500	328	CC-2V	3 1/2"	Card/2	120/10
60	B10	Cand.	<b>S3784</b>	60B10	Clear	120V	1500	672	CC-2V	3 3/4"	Card/2	120/10
60	B10	Cand.	<b>S3787</b>	60B10/F	Frosted	120V	1500	672	CC-2V	3 3/4"	Card/2	120/10
60	B10	Cand.	<b>S3790</b>	60B10/W	White	120V	1500	630	CC-2V	3 3/4"	Card/2	120/10

carded lamps

1500 Hours / 120 Volt



**Clear**

**S3764** 25 Watt  
**S3765** 40 Watt  
**S3766** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner



**Frosted**


**S3767** 25 Watt  
**S3768** 40 Watt  
**S3769** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	CA-10	Med.	<b>S3764</b>	25CA10	Clear	120V	1500	210	CC-2V	4 1/4"	Card/2	120/10
25	CA-10	Med.	<b>S3767</b>	25CA10/F	Frosted	120V	1500	200	CC-2V	4 1/4"	Card/2	120/10
40	CA-10	Med.	<b>S3765</b>	40CA10	Clear	120V	1500	370	CC-2V	4 1/4"	Card/2	120/10
40	CA-10	Med.	<b>S3768</b>	40CA10/F	Frosted	120V	1500	360	CC-2V	4 1/4"	Card/2	120/10
60	CA-10	Med.	<b>S3766</b>	60CA10	Clear	120V	1500	650	CC-2V	4 1/4"	Card/2	120/10
60	CA-10	Med.	<b>S3769</b>	60CA10/F	Frosted	120V	1500	640	CC-2V	4 1/4"	Card/2	120/10

carded lamps





# Torpedo *Medium Base*

## Carded Bulbs



1500 Hours / 120 Volt



**Clear**

**S3731** 25 Watt  
**S3732** 40 Watt  
**S3793** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner



**Frosted**

**S3734** 25 Watt  
**S3735** 40 Watt  
**S3796** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner



**White**

**S3737** 25 Watt  
**S3738** 40 Watt  
**S3799** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B11	Med.	<b>S3731</b>	25B11	Clear	120V	1500	210	CC-2V	3 7/8"	Card/2	120/10
25	B11	Med.	<b>S3734</b>	25B11/F	Frosted	120V	1500	200	CC-2V	3 7/8"	Card/2	120/10
25	B11	Med.	<b>S3737</b>	25B11/W	White	120V	1500	150	CC-2V	3 7/8"	Card/2	120/10
40	B11	Med.	<b>S3732</b>	40B11	Clear	120V	1500	370	CC-2V	3 7/8"	Card/2	120/10
40	B11	Med.	<b>S3735</b>	40B11/F	Frosted	120V	1500	360	CC-2V	3 7/8"	Card/2	120/10
40	B11	Med.	<b>S3738</b>	40B11/W	White	120V	1500	330	CC-2V	3 7/8"	Card/2	120/10
60	B11	Med.	<b>S3793</b>	60B11	Clear	120V	1500	650	CC-2V	3 7/8"	Card/2	120/10
60	B11	Med.	<b>S3796</b>	60B11/F	Frosted	120V	1500	640	CC-2V	3 7/8"	Card/2	120/10
60	B11	Med.	<b>S3799</b>	60B11/W	White	120V	1500	580	CC-2V	3 7/8"	Card/2	120/10

carded lamps

1500 Hours / 120 Volt



Clear

Frosted

E14  
European Base

- S4711 25 Watt
- S4712 40 Watt
- S4713 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner

specialty  
product

E14  
European Base

- S4714 25 Watt
- S4715 40 Watt
- S4716 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B9 1/2	Euro.	S4711	25B9 1/2	Clear	120V	1500	212	CC-2V	3 1/2"	Card/2	120/12
25	B9 1/2	Euro.	S4714	25B9 1/2/F	Frosted	120V	1500	212	CC-2V	3 1/2"	Card/2	120/12
40	B9 1/2	Euro.	S4712	40B9 1/2	Clear	120V	1500	384	CC-2V	3 1/2"	Card/2	120/12
40	B9 1/2	Euro.	S4715	40B9 1/2/F	Frosted	120V	1500	384	CC-2V	3 1/2"	Card/2	120/12
60	B10	Euro.	S4713	60B10	Clear	120V	1500	672	CC-2V	3 3/4"	Card/2	120/12
60	B10	Euro.	S4716	60B10/F	Frosted	120V	1500	672	CC-2V	3 3/4"	Card/2	120/12



# Turn-Tip *Candelabra Base*

**ALLURA®**

## *Carded* Bulbs

*2500 Hours / 130 Volt*

carded lamps

*Clear*

**A3573** 15 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



*Clear*

**A3574** 25 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



*Clear*

**A3562** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



*Clear*

**A3575** 40 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	CA-8	Cand.	<b>A3573</b>	15CA8	Clear	130V	2500	95	C-7A	3 5/8"	Card/2	120/10
25	CA-8	Cand.	<b>A3574</b>	25CA8	Clear	130V	2500	360	CC-2V	3 5/8"	Card/2	120/10
40	CA-9 1/2	Cand.	<b>A3575</b>	40CA9 1/2	Clear	130V	2500	370	CC-2V	3 15/16"	Card/2	120/10
60	CA-10	Cand.	<b>A3562</b>	60CA10	Clear	130V	2500	642	CC-2V	4 1/4"	Card/2	120/10

*2500 Hours / 130 Volt*



**Frosted**  
**A3577** 15 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Frosted**  
**A3578** 25 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Frosted**  
**A3579** 40 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Frosted**  
**A3563** 60 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
15	CA-8	Cand.	<b>A3577</b>	15CA8	Frosted	130V	2500	90	C-7A	3 5/8"	Card/2	120/10
25	CA-8	Cand.	<b>A3578</b>	25CA8	Frosted	130V	2500	200	CC-2V	3 5/8"	Card/2	120/10
40	CA-9 1/2	Cand.	<b>A3579</b>	40CA9 1/2	Frosted	130V	2500	350	CC-2V	3 15/16"	Card/2	120/10
60	CA-10	Cand.	<b>A3563</b>	60CA10	Frosted	130V	2500	635	CC-2V	4 1/4"	Card/2	120/10



# Torpedo *Candelabra Base*

**ALLURA®**

## Carded Bulbs

2500 Hours / 130 Volt

carded lamps

### Clear

**A3582** 25 Watt

**A3583** 40 Watt

**A3584** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



### Frosted

**A3585** 25 Watt

**A3586** 40 Watt

**A3587** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



### White

**A3588** 25 Watt

**A3589** 40 Watt

**A3590** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
25	B9 1/2	Cand.	<b>A3582</b>	25B9 1/2	Clear	130V	2500	193	CC-2V	3 1/2"	Card/2	120/10
25	B9 1/2	Cand.	<b>A3585</b>	25B9 1/2/F	Frosted	130V	2500	193	CC-2V	3 1/2"	Card/2	120/10
25	B9 1/2	Cand.	<b>A3588</b>	25B9 1/2/W	White	130V	2500	163	CC-2V	3 1/2"	Card/2	120/10
40	B9 1/2	Cand.	<b>A3583</b>	40B9 1/2	Clear	130V	2500	384	CC-2V	3 1/2"	Card/2	120/10
40	B9 1/2	Cand.	<b>A3586</b>	40B9 1/2/F	Frosted	130V	2500	384	CC-2V	3 1/2"	Card/2	120/10
40	B9 1/2	Cand.	<b>A3589</b>	40B9 1/2/W	White	130V	2500	328	CC-2V	3 1/2"	Card/2	120/10
60	B10	Cand.	<b>A3584</b>	60B10	Clear	130V	2500	642	CC-2V	3 3/4"	Card/2	120/10
60	B10	Cand.	<b>A3587</b>	60B10/F	Frosted	130V	2500	642	CC-2V	3 3/4"	Card/2	120/10
60	B10	Cand.	<b>A3590</b>	60B10/W	White	130V	2500	564	CC-2V	3 3/4"	Card/2	120/10

2500 Hours / 130 Volt



Clear

- A3564** 25 Watt
- A3565** 40 Watt
- A3566** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



Frosted

- A3567** 25 Watt
- A3568** 40 Watt
- A3569** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



### Shown Actual Size

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	CA-10	Med.	<b>A3564</b>	25CA10	Clear	130V	2500	210	CC-2V	4 1/4"	Card/2	120/10
25	CA-10	Med.	<b>A3567</b>	25CA10/F	Frosted	130V	2500	200	CC-2V	4 1/4"	Card/2	120/10
40	CA-10	Med.	<b>A3565</b>	40CA10	Clear	130V	2500	370	CC-2V	4 1/4"	Card/2	120/10
40	CA-10	Med.	<b>A3568</b>	40CA10/F	Frosted	130V	2500	360	CC-2V	4 1/4"	Card/2	120/10
60	CA-10	Med.	<b>A3566</b>	60CA10	Clear	130V	2500	650	CC-2V	4 1/4"	Card/2	120/10
60	CA-10	Med.	<b>A3569</b>	60CA10/F	Frosted	130V	2500	640	CC-2V	4 1/4"	Card/2	120/10

Carded lamps

# Torpedo *Medium Base*

## Carded Bulbs **ALLURA**<sup>®</sup>

2500 Hours / 130 Volt

carded lamps



**White**

**A3537** 25 Watt  
**A3538** 40 Watt  
**A3599** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner



**Frosted**

**A3534** 25 Watt  
**A3535** 40 Watt  
**A3596** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner



**Clear**

**A3531** 25 Watt  
**A3532** 40 Watt  
**A3593** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner

Shown Actual Size

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	B11	Med.	<b>A3531</b>	25B11	Clear	130V	2500	210	CC-2V	3 7/8"	Card/2	120/10
25	B11	Med.	<b>A3534</b>	25B11/F	Frosted	130V	2500	200	CC-2V	3 7/8"	Card/2	120/10
25	B11	Med.	<b>A3537</b>	25B11/W	White	130V	2500	160	CC-2V	3 7/8"	Card/2	120/10
40	B11	Med.	<b>A3532</b>	40B11	Clear	130V	2500	370	CC-2V	3 7/8"	Card/2	120/10
40	B11	Med.	<b>A3535</b>	40B11/F	Frosted	130V	2500	360	CC-2V	3 7/8"	Card/2	120/10
40	B11	Med.	<b>A3538</b>	40B11/W	White	130V	2500	320	CC-2V	3 7/8"	Card/2	120/10
60	B11	Med.	<b>A3593</b>	60B11	Clear	130V	2500	650	CC-2V	3 7/8"	Card/2	120/10
60	B11	Med.	<b>A3596</b>	60B11/F	Frosted	130V	2500	640	CC-2V	3 7/8"	Card/2	120/10
60	B11	Med.	<b>A3599</b>	60B11/W	White	130V	2500	550	CC-2V	3 7/8"	Card/2	120/10

# Candelabra Base Globe

## Carded Bulbs

1500 Hours / 120 Volt



**G16 1/2 2 1/8"**

**Clear**  
Candelabra Base  
(120 Volt)

- S3726** 15 Watt
- S3727** 25 Watt
- S3728** 40 Watt
- S3771** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**G16 1/2 2 1/8"**

**Satin White**  
Candelabra Base  
(120 Volt)

- S3752** 15 Watt
- S3753** 25 Watt
- S3754** 40 Watt
- S3772** 60 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**G12 1 1/2"**

**Satin White**  
Candelabra Base  
(120 Volt)

- S3755** 10 Watt
- S3750** 15 Watt
- S3751** 25 Watt

Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./Inner Pack
10	G12	Cand.	<b>S3755</b>	10G12/W	Sat. White	120V	1500	60	C7A	2 3/8"	Card/2	120/10
15	G12	Cand.	<b>S3750</b>	15G12/W	Sat. White	120V	1500	94	C7A	2 3/8"	Card/2	120/10
15	G16 1/2	Cand.	<b>S3726</b>	15G16 1/2	Clear	120V	1500	114	C7A	3"	Card/2	120/10
15	G16 1/2	Cand.	<b>S3752</b>	15G16 1/2/W	Sat. White	120V	1500	94	C7A	3"	Card/2	120/10
25	G12	Cand.	<b>S3751</b>	25G12/W	Sat. White	120V	1500	202	C7A	2 3/8"	Card/2	120/10
25	G16 1/2	Cand.	<b>S3727</b>	25G16 1/2	Clear	120V	1500	232	CC-2V	3"	Card/2	120/10
25	G16 1/2	Cand.	<b>S3753</b>	25G16 1/2/W	Sat. White	120V	1500	202	CC-2V	3"	Card/2	120/10
40	G16 1/2	Cand.	<b>S3728</b>	40G16 1/2	Clear	120V	1500	384	CC-2V	3"	Card/2	120/10
40	G16 1/2	Cand.	<b>S3754</b>	40G16 1/2/W	Sat. White	120V	1500	348	CC-2V	3"	Card/2	120/10
60	G16 1/2	Cand.	<b>S3771</b>	60G16 1/2	Clear	120V	1500	672	CC-2V	3"	Card/2	120/10
60	G16 1/2	Cand.	<b>S3772</b>	60G16 1/2/W	Sat. White	120V	1500	630	CC-2V	3"	Card/2	120/10

carded lamps





# Globe Brass Base

## Carded Bulbs



carded lamps

**G14 Clear**  
E14 Euro Base  
(130 Volt)  
**S4707** 40 Watt  
Packing: 2 Bulbs /Card  
120 Cards/Master,  
10 Cards/Inner



**G14 White**  
E14 Euro Base  
(130 Volt)  
**S4708** 40 Watt  
Packing:  
2 Bulbs /Card  
120 Cards/Master,  
10 Cards/Inner



**G16<sup>1/2</sup> Globe Light Clear**  
Medium Base 120V  
**S4538** 25 Watt Clear  
**S4539** 40 Watt Clear  
**S4540** 60 Watt Clear  
Packing: 1/Card  
120/Master, 10/Inner



**G16<sup>1/2</sup> Globe Light White**  
Medium Base 120V  
**S4541** 25 Watt White  
**S4542** 40 Watt White  
**S4543** 60 Watt White  
Packing: 1/Card  
120/Master, 10/Inner



**G17 Frosted**  
Medium Base  
(130 Volt)  
**S4709** 40 Watt  
Packing: 1 Bulb /Card  
120 Cards/Master,  
10 Cards/Inner



**G17 White**  
Medium Base  
(130 Volt)  
**S4710** 40 Watt  
Packing:  
1 Bulb /Card  
120 Cards/Master,  
10 Cards/Inner



Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
40	G14	Euro	S4707	40G14	Clear	130V	1000	360	CC-2V	2 5/8"	Card/2	120/10
40	G14	Euro	S4708	40G14/W	White	130V	1000	320	CC-2V	2 5/8"	Card/2	120/10
25	G16	Med.	S4538	25G16	Clear	120V	1500	210	CC-2V	3 1/4"	Card/1	120/10
25	G16	Med.	S4541	25G16/W	White	120V	1500	160	CC-2V	3 1/4"	Card/1	120/10
40	G16	Med.	S4539	40G16	Clear	120V	1500	370	CC-2V	3 1/4"	Card/1	120/10
40	G16	Med.	S4542	40G16/W	White	120V	1500	320	CC-2V	3 1/4"	Card/1	120/10
60	G16	Med.	S4540	60G16	Clear	120V	1500	650	CC-2V	3 1/4"	Card/1	120/10
60	G16	Med.	S4543	60G16/W	White	120V	1500	550	CC-2V	3 1/4"	Card/1	120/10
40	G17	Med.	S4709	40G17/F	Frosted	130V	1000	348	CC-2V	3 1/4"	Card/1	120/10
40	G17	Med.	S4710	40G17/W	White	130V	1000	348	CC-2V	3 1/4"	Card/1	120/10

*2500 Hours / 130 Volt*



**Clear**  
Candelabra Base  
(130 Volt)  
**A3521** 15 Watt  
**A3522** 25 Watt  
**A3523** 40 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



**Satin White**  
Candelabra Base  
(130 Volt)  
**A3524** 15 Watt  
**A3525** 25 Watt  
**A3526** 40 Watt  
Packing: 2 Bulbs/Card  
120 Cards/Master,  
10 Cards/Inner



*Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
15	G16 1/2	Cand.	<b>A3521</b>	15G16 1/2	Clear	130V	2500	98	C7A	3"	Card/2	120/10
15	G16 1/2	Cand.	<b>A3524</b>	15G16 1/2/W	White	130V	2500	83	C7A	3"	Card/2	120/10
25	G16 1/2	Cand.	<b>A3522</b>	25G16 1/2	Clear	130V	2500	186	C7A	3"	Card/2	120/10
25	G16 1/2	Cand.	<b>A3525</b>	25G16 1/2/W	White	130V	2500	162	C7A	3"	Card/2	120/10
40	G16 1/2	Cand.	<b>A3523</b>	40G16 1/2	Clear	130V	2500	360	CC-2V	3"	Card/2	120/10
40	G16 1/2	Cand.	<b>A3526</b>	40G16 1/2/W	White	130V	2500	325	CC-2V	3"	Card/2	120/10

carded lamps



Carded Bulbs

4000 Hours / 120 Volt

carded lamps



C11 Satin



C11 Amber



C15

Candelabra Base  
(120 Volt)

- S2703** 25 Watt
- S2704** 40 Watt
- S2705** 60 Watt

Packing: 1 Bulb/Card  
120 Cards/Master,  
12 Cards/Inner

Candelabra Base  
(120 Volt)

- S2706** 25 Watt
- Packing: 1 Bulb/Card  
120 Cards/Master,  
12 Cards/Inner

Medium Base  
(120 Volt)

- S2713** 25 Watt
- S2714** 40 Watt
- S2715** 60 Watt
- S2716** 40 Watt Amber


Packing: 1 Bulb/Card  
120 Cards/Master,  
12 Cards/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
25	C11	Cand.	<b>S2703</b>	25C11	Satin	120V	4000	160	C-7A	4"	Card/1	120/12
25	C11	Cand.	<b>S2706</b>	25C11/A	Amber	120V	4000	-	C-7A	4"	Card/1	120/12
40	C11	Cand.	<b>S2704</b>	40C11	Satin	120V	4000	316	C-7A	4"	Card/1	120/12
60	C11	Cand.	<b>S2705</b>	60C11	Satin	120V	4000	600	C-7A	4"	Card/1	120/12
25	C15	Med.	<b>S2713</b>	25C15	Satin	120V	4000	160	C-9	4 1/2"	Card/1	120/12
40	C15	Med.	<b>S2714</b>	40C15	Satin	120V	4000	316	C-9	4 1/2"	Card/1	120/12
40	C15	Med.	<b>S2716</b>	40C15/A	Amber	120V	4000	316	C-9	4 1/2"	Card/1	120/12
60	C15	Med.	<b>S2715</b>	60C15	Satin	120V	4000	606	C-9	4 1/2"	Card/1	120/12

1500 Hours

Not Shown Actual Size



### Clear

S2760 15 Watt  
S2771 25 Watt



### White

S2761 15 Watt  
S2772 25 Watt



### Aurora

S2773 25 Watt



### Amber

S2774 25 Watt



### F10

Candelabra Base  
(120 Volt)

Packing: 2 Bulbs to a Card  
120 Cards /Master, 12 Cards / Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
15	F10	Cand.	S2760	15F10	Clear	120V	1500	110	C-7A	3 1/16"	Card/2	120/12
15	F10	Cand.	S2761	15F10/W	White	120V	1500	90	C-7A	3 1/16"	Card/2	120/12
25	F10	Cand.	S2771	25F10	Clear	120V	1500	195	C-7A	3 1/16"	Card/2	120/12
25	F10	Cand.	S2772	25F10/W	White	120V	1500	185	C-7A	3 1/16"	Card/2	120/12
25	F10	Cand.	S2773	25F10/AU	Aurora	120V	1500	190	C-7A	3 1/16"	Card/2	120/12
25	F10	Cand.	S2774	25F10/A	Amber	120V	1500	-	C-7A	3 1/16"	Card/2	120/12



# F15 Flame *Brass Base*



## *Carded* Bulbs

1500 Hours

carded lamps



**F15**

Medium Base  
(120 Volt)

- S2763** 25 Watt Clear
- S2767** 40 Watt Clear
- S2764** 25 Watt White
- S2768** 40 Watt White
- S2765** 25 Watt Aurora
- S2769** 40 Watt Aurora
- S2770** 40 Watt Amber

Packing: 2 Bulbs to a Card  
120 Cards/Master,  
12 Cards/Inner



**White**



**Clear**




**Aurora**



**Amber**

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	F15	Med.	<b>S2763</b>	25F15	Clear	120V	1500	225	CC-9	4 1/2"	Card/2	120/12
25	F15	Med.	<b>S2764</b>	25F15/W	White	120V	1500	195	CC-9	4 1/2"	Card/2	120/12
25	F15	Med.	<b>S2765</b>	25F15/AU	Aurora	120V	1500	200	CC-9	4 1/2"	Card/2	120/12
40	F15	Med.	<b>S2767</b>	40F15	Clear	120V	1500	420	CC-9	4 1/2"	Card/2	120/12
40	F15	Med.	<b>S2768</b>	40F15/W	White	120V	1500	372	CC-9	4 1/2"	Card/2	120/12
40	F15	Med.	<b>S2769</b>	40F15/AU	Aurora	120V	1500	420	CC-9	4 1/2"	Card/2	120/12
40	F15	Med.	<b>S2770</b>	40F15/A	Amber	120V	1500	-	CC-9	4 1/2"	Card/2	120/12



**Krypton**

**Torpedo  
Clear**

Candelabra Base  
(120 Volt)

**S3716** 25 Watt

**S3717** 40 Watt

**S3718** 60 Watt

Packing: Card/2  
120/Master, 10/Inner

**Krypton**

*decorative bulbs*

create a brilliant sparkle,  
similar to the look of halogen .

Excellent for use in crystal  
chandeliers and fixtures with  
decorative glassware.

Additionally , krypton bulbs  
last longer than conventional  
lamps and maintain their  
lumen output during the  
full course of their life.



**Diamond Cut**

**Torpedo  
Clear**

Candelabra Base  
(120 Volt)

**S3725** 40 Watt

Packing: Card/2  
120/Master, 10/Inner

**Diamond Cut**

*decorative bulbs*

simulate the look of an  
illuminated crystal prism.  
These lamps will add a  
unique effect when used  
with crystal chandeliers.



**Silicone**

**S4520** 5 Watt  
Packing: Card/2  
144/Master, 12/Inner

**Silicone**

*decorative bulbs*

silicone dipped,  
perfect for decorative  
candle sconces and  
portable candle lamps.

*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
5	C7	Cand.	<b>S4520</b>	5C7	Silicone	120V	1000	10	C-7A	2 1/2+"	Card/2	144/12
25	B9 1/2	Cand.	<b>S3716</b>	KR25B9 1/2	Clear	120V	2500	210	CC-2V	3 7/8"	Card/2	120/10
40	B9 1/2	Cand.	<b>S3717</b>	KR40B9 1/2	Clear	120V	2500	370	CC-2V	3 7/8"	Card/2	120/10
60	B10	Cand.	<b>S3718</b>	KR60B10	Clear	120V	2500	640	CC-2V	3 7/8"	Card/2	120/10
40	B9 1/2	Cand.	<b>S3725</b>	40B9 1/2/DIA	Clear	120V	1500	370	CC-2V	3 7/8"	Card/2	120/10

# Ceiling *Brass Base* Fan Bulbs



2000 Hours

- High temperature base cement
- Vibration resistant filament

carded lamps



Clear



Frosted

**S4740** 40 Watt  
**S4741** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner

**S4742** 40 Watt  
**S4743** 60 Watt  
 Packing: 2 Bulbs/Card  
 120 Cards/Master,  
 10 Cards/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
40	B11	Med.	<b>S4740</b>	40B11/Fan	Clear	120V	2000	370	CC-2V	3 7/8"	Card/2	120/10
40	B11	Med.	<b>S4742</b>	40B11/Fan/F	Frosted	120V	2000	360	CC-2V	3 7/8"	Card/2	120/10
60	B11	Med.	<b>S4741</b>	60B11/Fan	Clear	120V	2000	650	CC-2V	3 7/8"	Card/2	120/10
60	B11	Med.	<b>S4743</b>	60B11/Fan/F	Frosted	120V	2000	640	CC-2V	3 7/8"	Card/2	120/10



*Brass Base* Prismatic

1500 Hours / 120 Volt

**Carded** Bulbs



**Aurora**



**Frosted**



**Clear**



Candelabra Base  
(120 Volt)

**S3748** 25 Watt  
**S3749** 40 Watt

**Packing:**  
2 Bulbs to a Card  
120 Cards/Master,  
12 Cards/Inner

Candelabra Base  
(120 Volt)

**S3746** 25 Watt  
**S3747** 40 Watt

**Packing:**  
2 Bulbs to a Card  
120 Cards/Master,  
12 Cards/Inner

Candelabra Base  
(120 Volt)

**S3744** 25 Watt  
**S3745** 40 Watt

**Packing:**  
2 Bulbs to a Card  
120 Cards/Master,  
12 Cards/Inner

*Not Shown  
Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Volts	Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	HX-101/2	Cand.	<b>S3744</b>	25HX101/2	Clear	120V	1500	175	C-7A	4 15/16"	Card/2	120/12
25	HX-101/2	Cand.	<b>S3746</b>	25HX101/2/F	Frosted	120V	1500	175	C-7A	4 15/16"	Card/2	120/12
25	HX-101/2	Cand.	<b>S3748</b>	25HX101/2/AU	Aurora	120V	1500	175	C-7A	4 15/16"	Card/2	120/12
40	HX-101/2	Cand.	<b>S3745</b>	40HX101/2	Clear	120V	1500	360	C-7A	4 15/16"	Card/2	120/12
40	HX-101/2	Cand.	<b>S3747</b>	40HX101/2/F	Frosted	120V	1500	360	C-7A	4 15/16"	Card/2	120/12
40	HX-101/2	Cand.	<b>S3749</b>	40HX101/2/AU	Aurora	120V	1500	360	C-7A	4 15/16"	Card/2	120/12

Carded lamps



# Carded Bulbs

1000 Hours /120 Volt



Candelabra Base  
**S3756** 3 Watt



Candelabra Base  
**S3759** 3 Watt



Medium Base  
**S3757** 3 Watt



Medium Base  
**S3760** 3 Watt



Candelabra Base  
**S3761** 3 Watt



Shown  
Actual Size

Packing:  
1 Bulb to a Card  
120 Cards/Master,  
12 Cards/Inner

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst.Ctn./ Inner Pack
3	CA-5 1/2	Cand.	<b>S3761</b>	3CA5 1/2/FLK	Clear	120V	1000	-	Flicker	3 1/4"	Card/1	120/12
3	CA-8	Cand.	<b>S3756</b>	3CA8/FLK	Clear	120V	1000	-	Flicker	3 7/8"	Card/1	120/12
3	B-9 1/2	Cand.	<b>S3759</b>	3B9 1/2/FLK	Clear	120V	1000	-	Flicker	3 1/2"	Card/1	120/12
3	CA-10	Med.	<b>S3757</b>	3CA10/FLK	Clear	120V	1000	-	Flicker	4 1/16"	Card/1	120/12
3	CA-9	Med.	<b>S3760</b>	3CA9/FLK	Clear	120V	1000	-	Flicker	4 9/16"	Card/1	120/12

carded lamps



T6 1/2



T6 1/2



T10



Intermediate Base  
(130 Volt)

- S3709** 25 Watt Clear
  - S3708** 25 Watt Frosted
  - S3710** 40 Watt Clear
  - S3712** 40 Watt Frosted
- Packing: 1 Bulb to a Card  
120 Cards/Master,  
10 Cards/Inner

D.C. Bayonet Base  
(130 Volt)

- S3711** 25 Watt Clear
  - S3713** 25 Watt Frosted
- Packing:  
1 Bulb to a Card  
120 Cards/Master,  
10 Cards/Inner

Medium Base  
(120 Volt)

- S3700** 25 Watt Clear
  - S3701** 25 Watt Frosted
  - S3702** 40 Watt Clear
  - S3703** 40 Watt Frosted
  - S3704** 60 Watt Clear
  - S3705** 60 Watt Frosted
- Packing: 1 Bulb to a Card  
120 Cards/Master,  
10 Cards/Inner

Not Shown  
Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	T6 1/2	DC Bay	<b>S3711</b>	25T6 1/2 DC	Clear	130V	1500	180	C-8	5 3/8"	Card/1	120/10
25	T6 1/2	DC Bay	<b>S3713</b>	25T6 1/2 DC/F	Frosted	130V	1500	170	C-8	5 3/8"	Card/1	120/10
25	T6 1/2	Int.	<b>S3709</b>	25T6 1/2 N	Clear	130V	1500	180	C-8	5 3/8"	Card/1	120/10
25	T6 1/2	Int.	<b>S3708</b>	25T6 1/2 N/F	Frosted	130V	1500	170	C-8	5 3/8"	Card/1	120/10
40	T6 1/2	Int.	<b>S3710</b>	40T6 1/2 N	Clear	130V	1500	350	C-8	5 3/8"	Card/1	120/10
40	T6 1/2	Int.	<b>S3712</b>	40T6 1/2 N/F	Frosted	130V	1500	340	C-8	5 3/8"	Card/1	120/10
25	T10	Med.	<b>S3700</b>	25T10	Clear	120V	1000	210	C-5V	5 3/16"	Card/1	120/10
25	T10	Med.	<b>S3701</b>	25T10/F	Frosted	120V	1000	200	C-5V	5 3/16"	Card/1	120/10
40	T10	Med.	<b>S3702</b>	40T10	Clear	120V	1000	300	C-5V	5 3/16"	Card/1	120/10
40	T10	Med.	<b>S3703</b>	40T10/F	Frosted	120V	1000	290	C-5V	5 3/16"	Card/1	120/10
60	T10	Med.	<b>S3704</b>	60T10	Clear	120V	1000	490	C-5V	5 3/16"	Card/1	120/10
60	T10	Med.	<b>S3705</b>	60T10/F	Frosted	120V	1000	480	C-5V	5 3/16"	Card/1	120/10

# Specialty Carded Bulbs



Not Shown Actual Size



**Hi Intensity  
S3723**  
12 Watt/15CP  
SC Bayonet Base  
12-16V  
Dom. Code #93  
Packing: 2 /Card  
240/Master, 20/Inner



**Hi Intensity  
S3729**  
40 Watt  
Intermediate Base  
115-125V  
Dom. Code #40S11N  
Packing: 2 /Card  
240/Master, 20/Inner



**Hi Intensity  
S3724**  
24 Watt/32 CP  
SC Bayonet Base  
6-8V  
Dom. Code #1133  
Packing: 2 /Card  
240/Master, 20/Inner



**7 1/2 S11**  
Medium Base  
(120 Volt)  
**S3794** 7 1/2 Watt Clear  
**S3795** 7 1/2 Watt White  
Packing: 1 Bulb/Card  
240 Cards/Master,  
20 Cards/Inner



**S11 Ceramic  
Colored Bulbs**  
Medium Base 120V  
**S4508** 7 1/2 Watt Blue  
**S4509** 7 1/2 Watt Green  
**S4510** 7 1/2 Watt Orange  
**S4511** 7 1/2 Watt Red  
**S4512** 7 1/2 Watt Yellow  
Packing: 1/Card  
120/Master, 10/Inner



**S14 Ceramic  
Colored Bulbs**  
Medium Base 130V  
**S4560** 11 Watt Yellow  
**S4561** 11 Watt Red  
**S4562** 11 Watt Green  
**S4563** 11 Watt Blue  
**S4564** 11 Watt Orange  
**S4565** 11 Watt Clear  
**S4566** 11 Watt White  
Packing: 1/Card  
120/Master, 10/Inner



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
7 1/2	S11	Med.	<b>S3794</b>	7 1/2 S11	Clear	120V	2500	40	C-7A	2 1/4"	Card/1	240/20
7 1/2	S11	Med.	<b>S3795</b>	7 1/2 S11/W	White	120V	2500	20	C-7A	2 1/4"	Card/1	240/20
7 1/2	S11	Med.	<b>S4508</b>	7 1/2 S11/B	Blue	120V	2500	-	C-7A	2 1/4"	1/Card	120/10
7 1/2	S11	Med.	<b>S4509</b>	7 1/2 S11/G	Green	120V	2500	-	C-7A	2 1/4"	1/Card	120/10
7 1/2	S11	Med.	<b>S4510</b>	7 1/2 S11/O	Orange	120V	2500	-	C-7A	2 1/4"	1/Card	120/10
7 1/2	S11	Med.	<b>S4511</b>	7 1/2 S11/R	Red	120V	2500	-	C-7A	2 1/4"	1/Card	120/10
7 1/2	S11	Med.	<b>S4512</b>	7 1/2 S11/Y	Yellow	120V	2500	-	C-7A	2 1/4"	1/Card	120/10
11	S14	Med.	<b>S4560</b>	11S14/Y	Yellow	130V	2500	80	CC-9	3 1/2"	1/Card	120/10
11	S14	Med.	<b>S4561</b>	11S14/R	Red	130V	2500	65	CC-9	3 1/2"	1/Card	120/10
11	S14	Med.	<b>S4562</b>	11S14/G	Green	130V	2500	-	CC-9	3 1/2"	1/Card	120/10
11	S14	Med.	<b>S4563</b>	11S14/B	Blue	130V	2500	-	CC-9	3 1/2"	1/Card	120/10
11	S14	Med.	<b>S4564</b>	11S14/O	Orange	130V	2500	-	CC-9	3 1/2"	1/Card	120/10
11	S14	Med.	<b>S4565</b>	11S14	Clear	130V	2500	-	CC-9	3 1/2"	1/Card	120/10
11	S14	Med.	<b>S4566</b>	11S14/W	White	130V	2500	-	CC-9	3 1/2"	1/Card	120/10
12	S8	S.C BAY/BA15S	<b>S3723</b>	12S8/93	Clear	12-16V	300	190	C-6	2 "	2/Card	240/20
24	RP11	S.C BAY/BA15S	<b>S3724</b>	24RP11/33	Clear	6-8V	300	400	C-6	2 1/4"	2/Card	240/20
40	S11	E17/Int.	<b>S3729</b>	40S11/N	Clear	115/125V	1500	370	CC-2V	2 3/8"	1/Card	240/20

carded lamps

# Night Light & Appliance Bulbs *Carded*



## 40A15/60A15

Medium Base  
(130 Volt)  
**S3720** 40 Watt Clear  
**S3721** 40 Watt Frosted  
**S3739** 60 Watt Clear  
**S3740** 60 Watt Frosted  
 Packing: 1 Bulb/Card  
 240 Cards/Master,  
 20 Cards/Inner



## 7C7 & 4C7

Candelabra Base  
(120 Volt)

### Two Pack

**S3797** 4 Watt Clear  
**S3791** 7 Watt Clear  
**S3792** 7 Watt White

Packing: 2 Bulbs/Card  
 400 Cards/Master,  
 20 Cards/Inner

### Four Pack

**S4724** 4 Watt Clear  
**S4725** 7 Watt Clear  
**S4726** 7 Watt White

Packing: 4 Bulbs/Card  
 48 Cards/Master,  
 12 Cards/Inner

Not Shown  
Actual Size



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./Inner Pack
4	C7	Cand.	<b>S3797</b>	4C7	Clear	120V	3000	16	C-7A	2 1/8"	Card/2	400/20
4	C7	Cand.	<b>S4724</b>	4C7	Clear	120V	3000	16	C-7A	2 1/8"	Card/4	48/12
7	C7	Cand.	<b>S3791</b>	7C7	Clear	120V	3000	35	C-7A	2 1/8"	Card/2	400/20
7	C7	Cand.	<b>S3792</b>	7C7/W	White	120V	3000	20	C-7A	2 1/8"	Card/2	400/20
7	C7	Cand.	<b>S4725</b>	7C7	Clear	120V	3000	35	C-7A	2 1/8"	Card/4	48/12
7	C7	Cand.	<b>S4726</b>	7C7/W	White	120V	3000	20	C-7A	2 1/8"	Card/4	48/12
40	A15	Med.	<b>S3720</b>	40A15	Clear	130V	2500	290	C-9	3 1/2"	Card/1	240/20
40	A15	Med.	<b>S3721</b>	40A15/F	Frosted	130V	2500	280	C-9	3 1/2"	Card/1	240/20
60	A15	Med.	<b>S3739</b>	60A15	Clear	130V	2500	580	C-9	3 1/2"	Card/1	240/20
60	A15	Med.	<b>S3740</b>	60A15/F	Frosted	130V	2500	530	C-9	3 1/2"	Card/1	240/20

Carded lamps

# Specialty Bulbs



## Carded

2500 Hours / 130 Volt

Clear Appliance, Indicator, Switchboard & Night Light



Indicator Bulb

**S4722** 15 Watt  
Int. Base/130 Volt  
Dom. Code #15T7/N



Appliance Bulb

**S4718** 15 Watt  
Cand. Base/130 Volt  
Dom. Code #15T7C



Indicator Bulb

**S4719** 15 Watt  
D.C. Bay. Base/130 Volt  
Dom. Code #15T7/DC



Appliance Bulb

**S4720** 25 Watt  
Int. Base/130 Volt  
Dom. Code #25T8N



Indicator Bulb

**S4721** 25 Watt  
D.C. Bay. Base/130 Volt  
Dom. Code #25T8DC



**Microwave  
Oven Bulb**  
**S3917** 40 Watt  
Int. Base/130 Volt  
Dom. Code #40T8N



**Indicator Bulb**  
**S4717** 6 Watt  
Cand. Base/130 Volt  
Dom. Code #6S6

Packing:  
2 Bulb/Card  
120 Cards/Master,  
12 Cards/Inner

Packing:  
1 Bulb/Card  
120 Cards/Master,  
12 Cards/Inner

Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
6	S6	Cand.	<b>S4717</b>	6S6	Clear	130V	2500	30	C-7A	1 7/8"	Card/2	120/12
15	T7	Cand.	<b>S4718</b>	15T7/C	Clear	130V	2500	95	C-5A	2 1/4"	Card/1	120/12
15	T7	Int.	<b>S4722</b>	15T7/N	Clear	130V	2500	95	C-5A	2 1/4"	Card/1	120/12
15	T7	DC Bayonet	<b>S4719</b>	15T7/DC	Clear	130V	2500	95	C-5A	2 1/4"	Card/1	120/12
25	T8	Int.	<b>S4720</b>	25T8/N	Clear	130V	2500	190	C-5A	2 5/8"	Card/1	120/12
25	T8	DC Bayonet	<b>S4721</b>	25T8/DC	Clear	130V	2500	190	C-5A	2 5/8"	Card/1	120/12
40	T8	Int.	<b>S3917</b>	40T8N	Clear	130V	2500	370	CC-2V	2 5/8"	Card/1	120/12

carded lamps

**Carded** R14 & R16

1500 Hours



**R14**

Medium Base  
120 Volt

**S4704** 25 Watt  
**S4705** 40 Watt

Packing: 1 Bulb/Card  
120 Cards/Master,  
10 Cards/Inner



**R14**

Intermediate Base  
120 Volt

**S4700** 25 Watt  
**S4701** 40 Watt

Packing: 1 Bulb/Card  
120 Cards/Master,  
10 Cards/Inner



**R16**

Medium Base  
120 Volt

**S4702** 40 Watt

Packing: 1 Bulb/Card  
120 Cards/Master,  
10 Cards/Inner



**R14**

Euro. (Mignon) Base  
130 Volt

**S4706** 40 Watt

Packing: 1 Bulb/Card  
120 Cards/Master,  
10 Cards/Inner

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
25	R14	Int.	<b>S4700</b>	25R14N	Lt. Frost	120V	1500	135	CC2V	2 5/8"	Card/1	120/10
25	R14	Med.	<b>S4704</b>	25R14	Lt. Frost	120V	1500	135	CC2V	2 5/8"	Card/1	120/10
40	R14	Euro	<b>S4706</b>	40R14	Lt. Frost	130V	1500	280	CC2V	2 5/8"	Card/1	120/10
40	R14	Int.	<b>S4701</b>	40R14N	Lt. Frost	120V	1500	280	CC2V	2 5/8"	Card/1	120/10
40	R14	Med.	<b>S4705</b>	40R14	Lt. Frost	120V	1500	280	CC2V	2 5/8"	Card/1	120/10
40	R16	Med.	<b>S4702</b>	40R16	Frost	120V	1500	280	C-9	3 7/16"	Card/1	120/10

Carded lamps



# Halogen MR11 & MR16



## Carded Lamps

**UV PROTECTED**  
NO HARMFUL  
ULTRAVIOLET  
RAYS

all carded  
halogen  
items feature  
UV protection

**2000 Hours**

carded lamps



### MR11

12 Volt Bi-Pin Base  
JRM Type

Promotional  
2/Pack

- S3464** 20 Watt SP FTC
- S3465** 20 Watt NFL FTD
- S3466** 35 Watt SP FTF
- S3467** 35 Watt NFL FTH

- S3424** 20 Watt NFL FTD
- S3425** 35 Watt NFL FTH

Packing:  
1 Bulb/Card  
12 Cards/Master,

Packing:  
2 Bulbs/Card  
12 Cards/Master



### MR16

12 Volt Bi-Pin Base  
JR Type

- S3460** 20 Watt SP ESX
- S3461** 20 Watt FL BAB
- S3462** 50 Watt SP EXT
- S3463** 50 Watt FL EXN

Packing:  
1 Bulb/Card  
12 Cards/Master,

Not Shown Actual Size


Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
20	MR11	GZ4	<b>S3464</b>	20MR11 FTC	SP 12°	12V	2000	1750	C-6	1 1/4"	Card/1	12
20	MR11	GZ4	<b>S3465</b>	20MR11 FTD	NFL 24°	12V	2000	700	C-6	1 1/4"	Card/1	12
20	MR11	GZ4	<b>S3424</b>	20MR11 FTD	NFL 24°	12V	2000	700	C-6	1 1/4"	Card/2	12
35	MR11	GZ4	<b>S3466</b>	35MR11 FTF	SP 12°	12V	2000	2500	C-6	1 1/4"	Card/1	12
35	MR11	GZ4	<b>S3467</b>	35MR11 FTH	NFL 24°	12V	2000	1550	C-6	1 1/4"	Card/1	12
35	MR11	GZ4	<b>S3425</b>	35MR11 FTH	NFL 24°	12V	2000	1550	C-6	1 1/4"	Card/2	12
20	MR16	GX5.3	<b>S3460</b>	20MR11 ESX	NSP 9°	12V	2000	4100	C-8	1 7/8"	Card/1	12
20	MR16	GX5.3	<b>S3461</b>	20MR11 BAB	FL 36°	12V	2000	700	C-6	1 7/8"	Card/1	12
50	MR16	GX5.3	<b>S3462</b>	50MR11 EXT	NSP 9°	12V	2000	10000	C-6	1 7/8"	Card/1	12
50	MR16	GX5.3	<b>S3463</b>	50MR11 EXN	FL 36°	12V	2000	1700	C-8	1 7/8"	Card/1	12

**2000 Hours**

all carded  
halogen  
items feature  
UV protection



## Carded Lamps



**BA15D**

**Double Contact**

- S3432** 75 Watt
- S3488** 100 Watt
- S3489** 150 Watt
- S3490** 250 Watt

Packing:  
1 Bulb/Card  
12 Cards/Master



**E14**

**European Base**

- S3491** 100 Watt
- S3492** 150 Watt
- S3493** 250 Watt

Packing:  
1 Bulb/Card  
12 Cards/Master



**E11**

**Mini Can**

- S3484** 75 Watt
- S3485** 100 Watt
- S3486** 150 Watt
- S3487** 250 Watt

Packing:  
1 Bulb/Card  
12 Cards/Master



Carded Lamps

*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
75	T4	E11	<b>S3484</b>	75Q/CL	Clear	120V	2000	1250	CC-8	2 11/16"	Card/1	12
75	T4	DC Bay	<b>S3432</b>	75Q/CL	Clear	120V	2000	1250	CC-8	2 13/32"	Card/1	12
100	T4	E11	<b>S3485</b>	100Q/CL	Clear	120V	2000	1600	CC-8	2 11/16"	Card/1	12
100	T4	DC Bay	<b>S3488</b>	100Q/CL	Clear	120V	2000	1600	CC-8	2 13/32"	Card/1	12
100	T4	E14	<b>S3491</b>	100Q/CL	Clear	120V	2000	1600	CC-8	2 15/16"	Card/1	12
150	T4	E11	<b>S3486</b>	150Q/CL	Clear	120V	2000	2400	CC-8	2 23/32"	Card/1	12
150	T4	DC Bay	<b>S3489</b>	150Q/CL	Clear	120V	2000	2400	CC-8	2 13/32"	Card/1	12
150	T4	E14	<b>S3492</b>	150Q/CL	Clear	120V	2000	2400	CC-8	3 1/32"	Card/1	12
250	T4.5	E11	<b>S3487</b>	250Q/CL	Clear	120V	2000	4350	CC-8	3 5/32"	Card/1	12
250	T4.5	DC Bay	<b>S3490</b>	250Q/CL	Clear	120V	2000	4350	CC-8	2 27/32"	Card/1	12
250	T4.5	E14	<b>S3493</b>	250Q/CL	Clear	120V	2000	4350	CC-8	3 11/32"	Card/1	12





# Halogen



## Carded Lamps



all carded halogen items feature UV protection

**2000 Hours**

**12 Volt**

**Promotional  
2/Pack**

**S3420** 20 Watt

**S3421** 50 Watt

Packing: 2 Bulbs/Card  
12 Cards/Master



**12 Volt**

**S3459** 10 Watt

**S3468** 20 Watt

**S3469** 35 Watt

**S3470** 50 Watt

**S3471** 75 Watt

Packing: 1 Bulb/Card  
12 Cards/Master



**120 Volt**

**G8 Base**

**S3540** 35 Watt

**S3541** 50 Watt

**S3542** 75 Watt

**S3543** 100 Watt

**120 Volt**

**G9 Base**

**S3544** 35 Watt

**S3545** 50 Watt

**S3546** 75 Watt

**S3547** 100 Watt

Packing: 1 Bulb/Card  
12 Cards/Master



G8 Base

G9 Base

GY6.35  
Base

**120 Volt**

**GY6.35 Base**

**S3418** 35 Watt

**S3427** 50 Watt

**S3428** 75 Watt

**S3419** 100 Watt

Packing: 1 Bulb/Card  
12 Cards/Master


**Not Shown  
Actual Size**

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Carton
10	T3	G4	<b>S3459</b>	10T3	Clear	12V	2000	120	C-6	32mm	Card/1	12
20	T3	G4	<b>S3468</b>	20T3	Clear	12V	2000	320	C-6	32mm	Card/1	12
20	T3	G4	<b>S3420</b>	20T3	Clear	12V	2000	320	C-6	32mm	Card/2	12
35	T4	GY6.35	<b>S3469</b>	35T4	Clear	12V	2000	600	C-6	41mm	Card/1	12
35	T4	GY6.35	<b>S3418</b>	35T4	Clear	120V	2000	400	C-6	50mm	Card/1	12
35	T4	G8	<b>S3540</b>	35T4	Clear	120V	2000	400	C-6	46mm	Card/1	12
35	T4	G9	<b>S3544</b>	35T4	Clear	120V	2000	400	C-6	45mm	Card/1	12
50	T4	GY6.35	<b>S3470</b>	50T4	Clear	12V	2000	900	C-6	41mm	Card/1	12
50	T4	GY6.35	<b>S3421</b>	50T4	Clear	12V	2000	900	C-6	41mm	Card/2	12
50	T4	GY6.35	<b>S3427</b>	50T4	Clear	120V	2000	750	CC-8	50mm	Card/1	12
50	T4	G8	<b>S3541</b>	50T4	Clear	120V	2000	750	CC-8	46mm	Card/1	12
50	T4	G9	<b>S3545</b>	50T4	Clear	120V	2000	750	CC-8	45mm	Card/1	12
75	T4	GY6.35	<b>S3471</b>	75T4	Clear	12V	2000	1350	C-6	41mm	Card/1	12
75	T4	GY6.35	<b>S3428</b>	75T4	Clear	120V	2000	1250	CC-8	60mm	Card/1	12
75	T4	G8	<b>S3542</b>	75T4	Clear	120V	2000	1250	CC-8	58mm	Card/1	12
75	T4	G9	<b>S3546</b>	75T4	Clear	120V	2000	1250	CC-8	56mm	Card/1	12
100	T4	GY6.35	<b>S3419</b>	100T4	Clear	120V	2000	1600	CC-8	60mm	Card/1	12
100	T4	G8	<b>S3543</b>	100T4	Clear	120V	2000	1600	CC-8	58mm	Card/1	12
100	T4	G9	<b>S3547</b>	100T4	Clear	120V	2000	1600	CC-8	56mm	Card/1	12

carded lamps

**2000 Hours**

all carded  
halogen  
items feature  
UV protection



**JDR Lensed**

**Medium  
Screw Base**

- S3438** 75W Flood
- S3439** 100W Flood

**Intermediate  
Screw Base**

- S3434** 75W Flood
- S3435** 100W Flood

Packing: 1 Bulb/Card  
12 Cards/Master



**Double -**

**JDD Envelope**

**Medium Base 120 Volt**

- S3472** 75 Watt Clear
- S3473** 100 Watt Clear
- S3474** 150 Watt Clear
- S3475** 250 Watt Clear
- S3476** 75 Watt Frosted
- S3477** 100 Watt Frosted
- S3478** 150 Watt Frosted
- S3479** 250 Watt Frosted

Packing: 1 Bulb/Card  
12 Cards/Master

**MR16 Twist Base  
GU10 Base 120 Volt**

- S3500** 20 Watt
- S3501** 35 Watt
- S3502** 50 Watt

Packing: 12 Cards/Inner  
120 Cards/Master



**Not Shown Actual Size**

carded lamps

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Carton
20	JCDR	GU10	<b>S3500</b>	20GU10/CL	Clear	120V	2000	1050	CC-8	1 7/8"	Card/1	12
35	JCDR	GU10	<b>S3501</b>	35GU10/CL	Clear	120V	2000	1000	CC-8	1 7/8"	Card/1	12
50	JCDR	GU10	<b>S3502</b>	50GU10/CL	Clear	120V	2000	1650	CC-8	1 7/8"	Card/1	12
75	T10	Med.	<b>S3472</b>	75T10Q/CL	Clear	120V	2000	1050	CC-8	4"	Card/1	12
75	T10	Med.	<b>S3476</b>	75T10Q/F	Frosted	120V	2000	1000	CC-8	4"	Card/1	12
75	JDR	INT.	<b>S3434</b>	75JDR/N/EXN	Clear	120V	2000	1650	CC-8	2 7/8"	Card/1	12
75	JDR	MED.	<b>S3438</b>	75JDR/EXN	Clear	120V	2000	1650	CC-8	2 7/8"	Card/1	12
100	JDR	INT.	<b>S3435</b>	100JDR/N/EXN	Clear	120V	2000	1950	CC-8	2 7/8"	Card/1	12
100	JDR	MED.	<b>S3439</b>	100JDR/EXN	Clear	120V	2000	1950	CC-8	2 7/8"	Card/1	12
100	T10	Med.	<b>S3473</b>	100T10Q/CL	Clear	120V	2000	1500	CC-8	4"	Card/1	12
100	T10	Med.	<b>S3477</b>	100T10Q/F	Frosted	120V	2000	1420	CC-8	4"	Card/1	12
150	T10	Med.	<b>S3474</b>	150T10Q/CL	Clear	120V	2000	2500	CC-8	4"	Card/1	12
150	T10	Med.	<b>S3478</b>	150T10Q/F	Frosted	120V	2000	2300	CC-8	4"	Card/1	12
250	T10	Med.	<b>S3475</b>	250T10Q/CL	Clear	120V	2000	4200	CC-8	4"	Card/1	12
250	T10	Med.	<b>S3479</b>	250T10Q/F	Frosted	120V	2000	3900	CC-8	4"	Card/1	12

# Halogen *Double Ended* Carded Lamps



all carded  
halogen  
items feature  
UV protection

2000 Hours



## 78MM J-Type (Short) 120V

**S3480** 100 Watt  
**S3481** 150 Watt  
**S3482** 200 Watt  
**S3426** 250 Watt

Packing:  
1 Bulb/Card  
12 Cards/Master



## 118MM J-Type (Long) 120V

**S3431** 100 Watt  
**S3494** 150 Watt  
**S3495** 200 Watt  
**S3496** 300 Watt

**S3497** 500 Watt  
Packing:  
1 Bulb/Card  
12 Cards/Master



Flat Blade

## 145MM J-Type (Blade) 120V

**S3429** 300 Watt

Packing: 1 Bulb/Card  
12 Cards/Master

### Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
100	T3	RS7	<b>S3480</b>	100T3Q/CL	Clear	120V	2000	1650	C-8	3 1/8"	Card/1	12
150	T3	RS7	<b>S3481</b>	150T3Q/CL	Clear	120V	2000	2600	C-8	3 1/8"	Card/1	12
200	T3	RS7	<b>S3482</b>	200T3Q/CL	Clear	120V	2000	3200	C-8	3 1/8"	Card/1	12
250	T3	RS7	<b>S3426</b>	250T3Q/CL	Clear	120V	2000	3950	C-8	3 1/8"	Card/1	12
100	T3	RS7	<b>S3431</b>	100T3Q/CL	Clear	120V	2000	1650	C-8	4 11/16"	Card/1	12
150	T3	RS7	<b>S3494</b>	150T3Q/CL	Clear	120V	2000	2600	C-8	4 11/16"	Card/1	12
200	T3	RS7	<b>S3495</b>	200T3Q/CL	Clear	120V	2000	3200	C-8	4 11/16"	Card/1	12
300	T3	RS7	<b>S3496</b>	300T3Q/CL	Clear	120V	2000	5000	C-8	4 11/16"	Card/1	12
500	T3	RS7	<b>S3497</b>	500T3Q/CL	Clear	120V	2000	9500	C-8	4 11/16"	Card/1	12
300	T3	Blade	<b>S3429</b>	300T3Q/CL	Clear	120V	2000	5000	C-8	5 13/16"	Card/1	12

carded lamps



# Halogen *Double Ended* Carded Lamps

2000 Hours

all carded halogen items feature UV protection



*Promotional Packs*



78MM J-Type Short (120V) 2 Pack

- S3422 100 Watt
- S3423 150 Watt

Packing:  
2 Bulbs/Card  
12 Cards/Master



118MM J-Type Long (120V) 2 Pack

- S3430 300 Watt
- S3433 500 Watt

Packing:  
2 Bulbs/Card  
12 Cards/Master



118MM J-Type Long (120V) 3 Pack

- S3410 300 Watt
- S3411 500 Watt

Packing:  
3 Bulbs/Card  
12 Cards/Master

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
100	T3	RS7	S3422	100T3Q/CL	Clear	120V	2000	1650	C-8	3 1/8"	Card/2	12
150	T3	RS7	S3423	150T3Q/CL	Clear	120V	2000	2600	C-8	3 1/8"	Card/2	12
300	T3	RS7	S3430	300T3Q/CL	Clear	120V	2000	3200	C-8	4 11/16"	Card/2	12
300	T3	RS7	S3410	300T3Q/CL	Clear	120V	2000	3200	C-8	4 11/16"	Card/3	12
500	T3	RS7	S3433	500T3Q/CL	Clear	120V	2000	9500	C-8	4 11/16"	Card/2	12
500	T3	RS7	S3411	500T3Q/CL	Clear	120V	2000	9500	C-8	4 11/16"	Card/3	12

Carded Lamps

# Compact Fluorescent Lamps



**10,000 Hours**



**Quad Tube**



**Twin Tube**

*Not Shown Actual Size*

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Pack. Type	Mst.Ctn./ InnerPack
<b>Two Pin Twin Tubes</b>										
5	T4	G23	<b>S6300</b>	CFS5W/827	2700K 82CRI	10000	230	4.2"	Box	50/5
7	T4	G23	<b>S6302</b>	CFS7W/827	2700K 82CRI	10000	400	5.3"	Box	50/5
9	T4	G23	<b>S6306</b>	CFS9W/827	2700K 82CRI	10000	580	6.5"	Box	50/5
13	T4	GX23	<b>S6310</b>	CFS13W/827	2700K 82CRI	10000	800	7.1"	Box	50/5
<b>Two Pin Quad Tubes</b>										
9	T4	G23-2	<b>S6314</b>	CFD9W/827	2700K 82CRI	10000	525	4.3"	Box	50/5
13	T4	GX23-2	<b>S6317</b>	CFD13W/827	2700K 82CRI	10000	780	4.6"	Box	50/5
18	T4	G24D-2	<b>S6321</b>	CFD18W/827	2700K 82CRI	10000	1250	6.0"	Box	50/5
26	T4	G24D-3	<b>S6325</b>	CFD26W/827	2700K 82CRI	10000	1825	6.8"	Box	50/5


For full selection see *Compact Fluorescent* section of catalog

carded lamps

# Fluorescent

## Sub-Miniature T2 Tubes

Not Shown Actual Size



**FM6**

**FM8**

**FM11**

**FM13**

**6 Watt**

**Axial Base**

**S6488** 3000K

**S2900** 3500K

**S6489** 4100K

Packing:

20/Master

**8 Watt**

**Axial Base**

**S6490** 3000K

**S2901** 3500K

**S6491** 4100K

Packing:

20/Master

**11 Watt**

**Axial Base**

**S6492** 3000K

**S2902** 3500K

**S6493** 4100K

Packing:

20/Master

**13 Watt**

**Axial Base**

**S6494** 3000K

**S2903** 3500K

**S6495** 4100K

Packing:

20/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Kelvin	CRI	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
6	T2	Axial	<b>S6488</b>	FM6/830	3000	80	10,000	330	8.6"	20
6	T2	Axial	<b>S2900</b>	FM6/835	3500	80	10,000	330	8.6"	20
6	T2	Axial	<b>S6489</b>	FM6/841	4100	80	10,000	330	8.6"	20
8	T2	Axial	<b>S6490</b>	FM8/830	3000	80	10,000	540	12.6"	20
8	T2	Axial	<b>S2901</b>	FM8/835	3500	80	10,000	540	12.6"	20
8	T2	Axial	<b>S6491</b>	FM8/841	4100	80	10,000	540	12.6"	20
11	T2	Axial	<b>S6492</b>	FM11/830	3000	80	10,000	750	16.6"	20
11	T2	Axial	<b>S2902</b>	FM11/835	3500	80	10,000	750	16.6"	20
11	T2	Axial	<b>S6493</b>	FM11/841	4100	80	10,000	750	16.6"	20
13	T2	Axial	<b>S6494</b>	FM13/830	3000	80	10,000	930	20.6"	20
13	T2	Axial	<b>S2903</b>	FM13/835	3500	80	10,000	930	20.6"	20
13	T2	Axial	<b>S6495</b>	FM13/841	4100	80	10,000	930	20.6"	20

# Fluorescent High Performance T5 Tubes



Not Shown Actual Size

Tri-Phosphor — Electronic Ballast

## Standard Mini Bi Pin Base

### 14W

S6425 3000K  
S6426 3500K  
S6427 4100K

### 21W

S6428 3000K  
S6429 3500K  
S6430 4100K

### 28W

S6431 3000K  
S6432 3500K  
S6433 4100K

### 35W

S6434 3000K  
S6435 3500K  
S6436 4100K

40/Master



## High Output Mini Bi Pin Base

### 24W

S6437 3000K  
S6438 3500K  
S6439 4100K

### 39W

S6440 3000K  
S6441 3500K  
S6442 4100K

### 54W

S6443 3000K  
S6444 3500K  
S6445 4100K

### 80W

S6446 3000K  
S6447 3500K  
S6448 4100K

40/Master

## Standard

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Kelvin	CRI	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
14	T5	Mini Bi Pin	S6425	FP14/830	3000	82	20,000	1275	24"	40
14	T5	Mini Bi Pin	S6426	FP14/835	3500	82	20,000	1275	24"	40
14	T5	Mini Bi Pin	S6427	FP14/841	4100	82	20,000	1275	24"	40
21	T5	Mini Bi Pin	S6428	FP21/830	3000	82	20,000	2000	36"	40
21	T5	Mini Bi Pin	S6429	FP21/835	3500	82	20,000	2000	36"	40
21	T5	Mini Bi Pin	S6430	FP21/841	4100	82	20,000	2000	36"	40
28	T5	Mini Bi Pin	S6431	FP28/830	3000	82	20,000	2750	48"	40
28	T5	Mini Bi Pin	S6432	FP28/835	3500	82	20,000	2750	48"	40
28	T5	Mini Bi Pin	S6433	FP28/841	4100	82	20,000	2750	48"	40
35	T5	Mini Bi Pin	S6434	FP35/830	3000	82	20,000	3425	60"	40
35	T5	Mini Bi Pin	S6435	FP35/835	3500	82	20,000	3425	60"	40
35	T5	Mini Bi Pin	S6436	FP35/841	4100	82	20,000	3425	60"	40

## High Output

24	T5	Mini Bi Pin	S6437	FP24/830/HO	3000	82	20,000	1875	24"	40
24	T5	Mini Bi Pin	S6438	FP24/835/HO	3500	82	20,000	1875	24"	40
24	T5	Mini Bi Pin	S6439	FP24/841/HO	4100	82	20,000	1875	24"	40
39	T5	Mini Bi Pin	S6440	FP39/830/HO	3000	82	20,000	3300	36"	40
39	T5	Mini Bi Pin	S6441	FP39/835/HO	3500	82	20,000	3300	36"	40
39	T5	Mini Bi Pin	S6442	FP39/841/HO	4100	82	20,000	3300	36"	40
54	T5	Mini Bi Pin	S6443	FP54/830/HO	3000	82	20,000	4725	48"	40
54	T5	Mini Bi Pin	S6444	FP54/835/HO	3500	82	20,000	4725	48"	40
54	T5	Mini Bi Pin	S6445	FP54/841/HO	4100	82	20,000	4725	48"	40
80	T5	Mini Bi Pin	S6446	FP80/830/HO	3000	82	20,000	6575	60"	40
80	T5	Mini Bi Pin	S6447	FP80/835/HO	3500	82	20,000	6575	60"	40
80	T5	Mini Bi Pin	S6448	FP80/841/HO	4100	82	20,000	6575	60"	40

fluorescent lamps

# Fluorescent T5 Tubes Preheat



5000 Hours

Not Shown Actual Size



**Blacklights**

**F4T5**

**F6T5**

**F8T5**

**F13T5**

**Blacklight**

- S2904 4 Watt
- S2905 6 Watt
- S2906 8 Watt

**Blacklight Blue**

- S6405 4 Watt
- S2907 6 Watt
- S6406 8 Watt

Packing: 24/Master,  
Individually Boxed

**4 Watt**

- Mini Bi Pin Base
- S1900 Cool White
- S2908 Daylight

Packing: 20/Master,  
Individually Boxed

**6 Watt**

- Mini Bi Pin Base
- S1902 Cool White
- S2909 Daylight

Packing: 20/Master,  
Individually Boxed

**8 Watt**

- Mini Bi Pin Base
- S1904 Cool White
- S1905 Warm White
- S2910 Daylight

Packing: 20/Master,  
Individually Boxed

**13 Watt**

- Mini Bi Pin Base
- S1906 Cool White
- S1907 Warm White
- S2911 Daylight

Packing: 20/Master,  
Individually Boxed

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Pack. Type	Carton
4	T5	Mini Bi Pin	S1900	F4T5/CW	Cool White	5000	135	6"	Box	20
4	T5	Mini Bi Pin	S2908	F4T5/D	Daylight	5000	115	6"	Box	20
4	T5	Mini Bi Pin	S2904	F4T5/BL	Blacklight	5000	n/a	6"	Sleeve	20
4	T5	Mini Bi Pin	S6405	F4T5/BLB	Blacklight Blue	5000	n/a	6"	Sleeve	20
6	T5	Mini Bi Pin	S1902	F6T5/CW	Cool White	5000	270	9"	Box	20
6	T5	Mini Bi Pin	S2909	F6T5/D	Daylight	5000	260	9"	Box	20
6	T5	Mini Bi Pin	S2905	F6T5/BL	Blacklight	5000	n/a	9"	Sleeve	20
6	T5	Mini Bi Pin	S2907	F6T5/BLB	Blacklight Blue	5000	n/a	9"	Sleeve	20
8	T5	Mini Bi Pin	S1904	F8T5/CW	Cool White	5000	390	12"	Box	20
8	T5	Mini Bi Pin	S2910	F8T5/D	Daylight	5000	350	12"	Box	20
8	T5	Mini Bi Pin	S1905	F8T5/WW	Warm White	5000	400	12"	Box	20
8	T5	Mini Bi Pin	S2906	F8T5/BL	Blacklight	5000	n/a	12"	Sleeve	20
8	T5	Mini Bi Pin	S6406	F8T5/BLB	Blacklight Blue	5000	n/a	12"	Sleeve	20
13	T5	Mini Bi Pin	S1906	F13T5/CW	Cool White	5000	860	21"	Box	20
13	T5	Mini Bi Pin	S2911	F13T5/D	Daylight	5000	780	21"	Box	20
13	T5	Mini Bi Pin	S1907	F13T5/WW	Warm White	5000	870	21"	Box	20

fluorescent lamps



# Fluorescent T8 Tubes Preheat

Not Shown Actual Size



**F30T8**

**30 Watt 36"**  
**Medium Bi Pin Base**

- S6517** Cool White
- S6518** Daylight
- S6519** Warm White

Packing: 24/Master



**F18T8**

**T8 Appliance**  
**Medium Bi Pin Base**

- S6513** Cool White/24"
- S6514** Cool White/26"
- S6515** Cool White/28"
- S6516** Cool White/30"

Packing: 24/Master



**F15T8**

**15 Watt 18"**  
**Medium Bi Pin Base**

- S6510** Cool White
- S6511** Daylight
- S6512** Warm White
- S6665** Full Spectrum\*

Packing: 24/Master  
\*6/Master



**F15T8**

**15 Watt 18"**  
**Medium Bi Pin Base**

- S6407** Black Light Blue
- S2918** Black Light

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
15	T8	Med. Bi Pin	<b>S6510</b>	F15T8/CW	Cool White	7500	850	18"	24
15	T8	Med. Bi Pin	<b>S6511</b>	F15T8/D	Daylight	7500	750	18"	24
15	T8	Med. Bi Pin	<b>S6512</b>	F15T8/WW	Warm White	7500	845	18"	24
15	T8	Med. Bi Pin	<b>S6665</b>	F15T8/SUN	Full Spectrum	12000	600	18"	6
15	T8	Med. Bi Pin	<b>S2918</b>	F15T8/BL	Black Light	7500	n/a	18"	25
15	T8	Med. Bi Pin	<b>S6407</b>	F15T8/BLB	Black Light Blue	7500	n/a	18"	20
18	T8	Med. Bi Pin	<b>S6513</b>	F18T8/CW/K/24	Cool White	7500	1190	24"	24
18	T8	Med. Bi Pin	<b>S6514</b>	F18T8/CW/K/26	Cool White	7500	1240	26"	24
18	T8	Med. Bi Pin	<b>S6515</b>	F18T8/CW/K/28	Cool White	7500	1240	28"	24
18	T8	Med. Bi Pin	<b>S6516</b>	F18T8/CW/K/30	Cool White	7500	1300	30"	24
30	T8	Med. Bi Pin	<b>S6517</b>	F30T8/CW	Cool White	7500	1380	36"	24
30	T8	Med. Bi Pin	<b>S6518</b>	F30T8/D	Daylight	7500	2180	36"	24
30	T8	Med. Bi Pin	<b>S6519</b>	F30T8/WW	Warm White	7500	2150	36"	24

fluorescent lamps

## T8 Electronic Tubes

20,000 Hours

### ENVIRONMENTALLY FRIENDLY SATCO T8 ELECTRONIC

fluorescent lamps are designed to meet the Federal Toxicity Characteristic Leaching Procedure (TCLP) criteria for classification as non-hazardous waste in most states\*.



- Designed to pass Federal TCLP test\*.
- Energy efficient T8 lamp.
- Available in 3000K, 3500K, 4100K, 5000K & 6500K
- 20,000–hours average life time.
- 700 Series lamps equal: 75CRI Good Color Rendition
- 800 Series lamps equal: 80-82 CRI Superior Color Rendition

\*Regulations may vary. Check your local and state regulations.

Not Shown Actual Size

#### 700 SERIES

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
32	T8	Med. Bi Pin	S6617	F32T8/730/ENV	3000K 75CRI	20000	2800	48"	30
32	T8	Med. Bi Pin	S6618	F32T8/735/ENV	3500K 75CRI	20000	2800	48"	30
32	T8	Med. Bi Pin	S6619	F32T8/741/ENV	4100K 75CRI	20000	2800	48"	30
32	T8	Med. Bi Pin	S6694	F32T8/750/ENV	5000K 75CRI	20000	2650	48"	30
32	T8	Med. Bi Pin	S6695	F32T6/765/ENV	6500K 75CRI	20000	2700	48"	30

#### 800 SERIES

32	T8	Med. Bi Pin	S6401	F32T8/830/ENV	3000K 82CRI	20000	2950	48"	30
32	T8	Med. Bi Pin	S6402	F32T8/835/ENV	3500K 82CRI	20000	2950	48"	30
32	T8	Med. Bi Pin	S6403	F32T8/841/ENV	4100K 82CRI	20000	2950	48"	30
32	T8	Med. Bi Pin	S6404	F32T8/850/ENV	5000K 80CRI	20000	2800	48"	30

# Eco Fluorescent T8 Electronic Tubes

**Color Reference Guide:**  
 730/830 = 3000K Warm White  
 735/835 = 3500K Neutral  
 741/841 = 4100K Cool White  
 750/850 = 5000K Daylight  
 765/865 = 6500K Daylight

700 Series lamps equal: 75CRI\*  
 Good color rendition

800 Series lamps equal: 80-85CRI\*  
 Superior color rendition

(Color rendering index\*)





**F32T8**

32 Watt 48"  
Medium Bi Pin Base

**F25T8**

25 Watt 36"  
Medium Bi Pin Base

**F17T8**

17 Watt 24"  
Medium Bi Pin Base

Not Shown  
Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Carton
17	T8	Med. Bi Pin	S6520	FO17/730/ECO	3000K 75CRI	20000	1300	24"	30
17	T8	Med. Bi Pin	S6523	FO17/830/ECO	3000K 82CRI	20000	1350	24"	30
17	T8	Med. Bi Pin	S6521	FO17/735/ECO	3500K 75CRI	20000	1300	24"	30
17	T8	Med. Bi Pin	S6524	FO17/835/ECO	3500K 82CRI	20000	1350	24"	30
17	T8	Med. Bi Pin	S6522	FO17/741/ECO	4100K 75CRI	20000	1300	24"	30
17	T8	Med. Bi Pin	S6525	FO17/841/ECO	4100K 82CRI	20000	1350	24"	30
17	T8	Med. Bi Pin	S2913	F17T8/SUN	6280K 95CRI	14000	750	24"	6
25	T8	Med. Bi Pin	S6526	FO25/730/ECO	3000K 75CRI	20000	1950	36"	30
25	T8	Med. Bi Pin	S6529	FO25/830/ECO	3000K 82CRI	20000	2150	36"	30
25	T8	Med. Bi Pin	S6527	FO25/735/ECO	3500K 75CRI	20000	1950	36"	30
25	T8	Med. Bi Pin	S6530	FO25/835/ECO	3500K 82CRI	20000	2150	36"	30
25	T8	Med. Bi Pin	S6528	FO25/741/ECO	4100K 75CRI	20000	1950	36"	30
25	T8	Med. Bi Pin	S6531	FO25/841/ECO	4100K 82CRI	20000	2150	36"	30
25	T8	Med. Bi Pin	S2914	F25T8/SUN	6280K 95CRI	14000	1200	36"	6
32	T8	Med. Bi Pin	S6532	FO32/730/ECO	3000K 75CRI	20000	2800	48"	30
32	T8	Med. Bi Pin	S6535	FO32/830/ECO	3000K 82CRI	20000	2950	48"	30
32	T8	Med. Bi Pin	S2915	FO32/830XP/ECO	3000K 85CRI	24000	3000	48"	30
32	T8	Med. Bi Pin	S6533	FO32/735/ECO	3500K 75CRI	20000	2800	48"	30
32	T8	Med. Bi Pin	S6536	FO32/835/ECO	3500K 82CRI	20000	2950	48"	30
32	T8	Med. Bi Pin	S2916	FO32/835XP/ECO	3500K 85CRI	24000	3000	48"	30
32	T8	Med. Bi Pin	S6534	FO32/741/ECO	4100K 75CRI	20000	2800	48"	30
32	T8	Med. Bi Pin	S6537	FO32/841/ECO	4100K 82CRI	20000	2950	48"	30
32	T8	Med. Bi Pin	S2917	FO32/841XP/ECO	4100K 85CRI	24000	3000	48"	30
32	T8	Med. Bi Pin	S2918	FO32/750/ECO	5000K 75CRI	20000	2650	48"	30
32	T8	Med. Bi Pin	S2919	FO32/850/ECO	5000K 80CRI	20000	2800	48"	30
32	T8	Med. Bi Pin	S2920	FO32/850XP/ECO	5000K 85CRI	24000	3000	48"	30
32	T8	Med. Bi Pin	S2921	FO32/765/ECO	6500K 75CRI	20000	2700	48"	30
32	T8	Med. Bi Pin	S2922	F32T8/SUN	6000K 85CRI	20000	2900	48"	12

fluorescent lamps

# Fluorescent T8 Electronic Tubes

700 Series lamps equal: 75CRI\*  
Good color rendition

800 Series lamps equal: 82CRI\*  
Superior color rendition

(Color rendering index\*)



**FO40 5 ft.**

**40 Watt 60"**  
Medium Bi Pin Base

"700" Series

**S6544** FO40/730

**S6545** FO40/735

**S6546** FO40/741

"800" Series

**S6547** FO40/830

**S6548** FO40/835

**S6549** FO40/841

Packing: 30/Master

### Color Reference Guide:

730/830 = 3000K Warm White

735/835 = 3500K Neutral

741/841 = 4100K Cool White



**FO96 8 ft.**

**59 Watt 96"**  
Single Pin Base

"700" Series

**S6538** FO96/730

**S6539** FO96/735

**S6540** FO96/741

"800" Series

**S6541** FO96/830

**S6542** FO96/835

**S6543** FO96/841

Packing: 24/Master

### Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
40	T8	Med. Bi Pin	<b>S6544</b>	FO40/730	3000K 75CRI	20000	3500	60"	30
40	T8	Med. Bi Pin	<b>S6545</b>	FO40/735	3500K 75CRI	20000	3500	60"	30
40	T8	Med. Bi Pin	<b>S6546</b>	FO40/741	4100K 75CRI	20000	3500	60"	30
40	T8	Med. Bi Pin	<b>S6547</b>	FO40/830	3000K 82CRI	20000	3650	60"	30
40	T8	Med. Bi Pin	<b>S6548</b>	FO40/835	3500K 82CRI	20000	3650	60"	30
40	T8	Med. Bi Pin	<b>S6549</b>	FO40/841	4100K 82CRI	20000	3650	60"	30
59	T8	Single Pin	<b>S6538</b>	FO96/730	3000K 75CRI	15000	5700	96"	24
59	T8	Single Pin	<b>S6539</b>	FO96/735	3500K 75CRI	15000	5700	96"	24
59	T8	Single Pin	<b>S6540</b>	FO96/741	4100K 75CRI	15000	5700	96"	24
59	T8	Single Pin	<b>S6541</b>	FO96/830	3000K 82CRI	15000	5900	96"	24
59	T8	Single Pin	<b>S6542</b>	FO96/835	3500K 82CRI	15000	5900	96"	24
59	T8	Single Pin	<b>S6543</b>	FO96/841	4100K 82CRI	15000	5900	96"	24

# Fluorescent

## 20,000 Hours **T8 Electronic** U Bend Tubes



700 Series lamps  
equal: 75CRI\*  
Good color  
rendition

800 Series lamps  
equal: 82CRI\*  
Superior color  
rendition

(Color rendering index\*)

### Color Reference Guide:

730/830 = 3000K Warm White

735/835 = 3500K Neutral

741/841 = 4100K Cool White



**FBO31**  
1 5/8" Leg Spacing

**31 Watt**  
Medium Bi Pin Base

"800" Series

**S6550** FBO31/830

**S6551** FBO31/835

**S6552** FBO31/841

**S2923** FBO31/750

Packing: 15/Master

Not Shown  
Actual Size



**FBO32/6**  
6" Leg Spacing

**32 Watt**  
Medium Bi Pin Base

"700" Series

"800" Series

**S6553** FBO32/730/6

**S6556** FBO32/830/6

**S6554** FBO32/735/6

**S6557** FBO32/835/6

**S6555** FBO32/741/6

**S6558** FBO32/841/6

**S2924** FBO32/750/6

Packing: 16/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Leg Spacing	Initial Lumens	Nominal Length	Carton
31	T8	Med. Bi Pin	<b>S6550</b>	FBO31/830	3000K 82CRI	20000	1 5/8"	2725	22 1/2"	15
31	T8	Med. Bi Pin	<b>S6551</b>	FBO31/835	3500K 82CRI	20000	1 5/8"	2725	22 1/2"	15
31	T8	Med. Bi Pin	<b>S6552</b>	FBO31/841	4100K 82CRI	20000	1 5/8"	2725	22 1/2"	15
31	T8	Med. Bi Pin	<b>S2923</b>	FBO31/750	5000K 75CRI	20000	1 5/8"	2600	22 1/2"	15
32	T8	Med. Bi Pin	<b>S6553</b>	FBO32/730/6	3000K 75CRI	20000	6"	2750	22 1/2"	16
32	T8	Med. Bi Pin	<b>S6556</b>	FBO32/830/6	3000K 82CRI	20000	6"	2850	22 1/2"	16
32	T8	Med. Bi Pin	<b>S6554</b>	FBO32/735/6	3500K 75CRI	20000	6"	2750	22 1/2"	16
32	T8	Med. Bi Pin	<b>S6557</b>	FBO32/835/6	3500K 82CRI	20000	6"	2850	22 1/2"	16
32	T8	Med. Bi Pin	<b>S6555</b>	FBO32/741/6	4100K 75CRI	20000	6"	2750	22 1/2"	16
32	T8	Med. Bi Pin	<b>S6558</b>	FBO32/841/6	4100K 82CRI	20000	6"	2850	22 1/2"	16
32	T8	Med. Bi Pin	<b>S2924</b>	FBO32/750/6	5000K 75CRI	20000	6"	2625	22 1/2"	16

fluorescent lamps

# Fluorescent T12 Tubes Preheat

7500 Hours

fluorescent lamps



**F14T12**

**14 Watt 15"**  
**Medium Bi Pin Base**  
**S6559** Cool White  
**S6560** Daylight  
**S6561** Warm White

Packing:  
30/Master



**F15T12**

**15 Watt 18"**  
**Medium Bi Pin Base**  
**S6562** Cool White  
**S6563** Daylight  
**S6564** Warm White

Packing:  
30/Master

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
14	T12	Med. Bi Pin	<b>S6559</b>	F14T12/CW	Cool White	7500	650	15"	30
14	T12	Med. Bi Pin	<b>S6560</b>	F14T12/D	Daylight	7500	590	15"	30
14	T12	Med. Bi Pin	<b>S6561</b>	F14T12/WW	Warm White	7500	660	15"	30
15	T12	Med. Bi Pin	<b>S6562</b>	F15T12/CW	Cool White	7500	750	18"	30
15	T12	Med. Bi Pin	<b>S6563</b>	F15T12/D	Daylight	7500	660	18"	30
15	T12	Med. Bi Pin	<b>S6564</b>	F15T12/WW	Warm White	7500	770	18"	30

# Fluorescent T12 Tubes

Not Shown Actual Size



**F30T12**

**30 Watt 36"**  
Rapid Start  
Medium Bi Pin Base  
**S6571** Cool White  
**S6572** Day Light  
**S6573** Warm White  
**S6574** F30T12/D830  
**S6575** F30T12/D35  
**S6576** F30T12/D41  
**S6667** Full Spectrum\*  
Packing: 30/Master  
\*6/Master



**F25T12**

**25 Watt**  
Preheat  
Appliance  
Medium Bi Pin Base  
**S6568** Cool White/28"  
**S6569** Cool White/30"  
**S6570** Cool White/33"  
Packing: 30/Master



**F20T12**

**20 Watt 24"**  
Preheat  
General Purpose  
Medium Bi Pin Base  
**S6565** Cool White  
**S6566** Daylight  
**S6567** Warm White  
**S6666** Full Spectrum\*  
Packing: 30/Master  
6/Master\*



**F20T12/F40T12  
Blacklights**

**20 Watt T12 24"**  
Preheat  
Medium Bi Pin Base  
**S6408** Blacklight Blue  
**S2925** Blacklight  
  
**40 Watt T12 48"**  
Rapid Start  
Medium Bi Pin Base  
**S6409** Blacklight Blue\*  
**S2926** Blacklight  
Packing: 30/Master  
\*6/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
20	T12	Med. Bi Pin	<b>S6565</b>	F20T12/CW	Cool White	9000	1220	24"	30
20	T12	Med. Bi Pin	<b>S6566</b>	F20T12/D	Daylight	9000	1075	24"	30
20	T12	Med. Bi Pin	<b>S6567</b>	F20T12/WW	Warm White	9000	1250	24"	30
20	T12	Med. Bi Pin	<b>S6666</b>	F20T12/SUN	Full Spectrum	14000	800	24"	6
20	T12	Med. Bi Pin	<b>S6408</b>	F20T12/BLB	Blacklight Blue	9000	n/a	24"	30
20	T12	Med. Bi Pin	<b>S2925</b>	F20T12/BL	Blacklight	9000	n/a	24"	30
25	T12	Med. Bi Pin	<b>S6568</b>	F25T12/CW/28"	Cool White	7500	1670	28"	30
25	T12	Med. Bi Pin	<b>S6569</b>	F25T12/CW/30"	Cool White	7500	1730	30"	30
25	T12	Med. Bi Pin	<b>S6570</b>	F25T12/CW/33"	Cool White	7500	1750	33"	30
30	T12	Med. Bi Pin	<b>S6571</b>	F30T12/CW/RS	Cool White	18000	2200	36"	30
30	T12	Med. Bi Pin	<b>S6572</b>	F30T12/D/RS	Daylight	18000	1900	36"	30
30	T12	Med. Bi Pin	<b>S6573</b>	F30T12/WW/RS	Warm White	18500	2275	36"	30
30	T12	Med. Bi Pin	<b>S6574</b>	F30T12/D830/RS	3000K 80CRI	18000	2290	36"	30
30	T12	Med. Bi Pin	<b>S6575</b>	F30T12/D35/RS	3500K 70CRI	18000	2250	36"	30
30	T12	Med. Bi Pin	<b>S6576</b>	F30T12/D41/RS	4100K 70CRI	18000	2250	36"	30
30	T12	Med. Bi Pin	<b>S6667</b>	F30T12/SUN	Full Spectrum	22000	1650	36"	30
40	T12	Med. Bi Pin	<b>S6409</b>	F40T12/BLB	Blacklight Blue	10000	n/a	48"	6
40	T12	Med. Bi Pin	<b>S2926</b>	F40T12/BL	Blacklight	10000	n/a	48"	30

fluorescent lamps

# Fluorescent T12 Tubes

Not Shown Actual Size

## F34T12/SS

(Previously F40T12/SS)

34 Watt 48"  
Energy Savers  
Medium Bi Pin Base

**S6600** F34T12/Cool White/SS  
**S6601** F34T12/Warm White/SS

### Designer Series

**S6602** F34T12/D30/SS  
**S6603** F34T12/D35/SS  
**S6604** F34T12/D41/SS

### Designer 800 Series

**S6605** F34T12/D830/SS  
**S6606** F34T12/D835/SS  
**S6607** F34T12/D841/SS

### Color Reference Guide

D30/D830 = 3000K Warm White  
D35/D835 = 3500K Neutral  
D41/D841 = 4100K Cool White

700 Series lamps equal: 70CRI\*  
Good color rendition

800 Series lamps equal: 80CRI\*  
Superior color rendition

(Color rendering index\*)

## F40T12

40 Watt 48"  
Standard Wattage  
Medium Bi Pin Base

**S2927** F40T12/Cool White Deluxe  
**S6608** F40T12/Daylight Deluxe  
**S6609** F40T12/Natural White  
**S6610** F40T12/Design 50  
**S6668** F40T12/Full Spectrum

### Designer Series

**S6611** F40T12/D30  
**S6612** F40T12/D35  
**S6613** F40T12/D41

### Designer 800 Series

**S6614** F40T12/D830  
**S6615** F40T12/D835  
**S6616** F40T12/D841  
**S2928** F40T12/D865

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Mst.Ctn./ Inner Pack
34	T12	Med. Bi Pin	<b>S6600</b>	F34/CW/SS	CW 4200K 62CRI	20000	2650	48"	30
34	T12	Med. Bi Pin	<b>S6601</b>	F34/WW/SS	WW 3000K 52 CRI	20000	2750	48"	30
34	T12	Med. Bi Pin	<b>S6602</b>	F34/D30/SS	3000K 70CRI	20000	2800	48"	30
34	T12	Med. Bi Pin	<b>S6605</b>	F34/D830/SS	3000K 80CRI	20000	2900	48"	30
34	T12	Med. Bi Pin	<b>S6603</b>	F34/D35/SS	3500K 70CRI	20000	2800	48"	30
34	T12	Med. Bi Pin	<b>S6606</b>	F34/D835/SS	3500K 80CRI	20000	2900	48"	30
34	T12	Med. Bi Pin	<b>S6604</b>	F34/D41/SS	4100K 70CRI	20000	2800	48"	30
34	T12	Med. Bi Pin	<b>S6607</b>	F34/D841/SS	4100K 80CRI	20000	2900	48"	30
40	T12	Med. Bi Pin	<b>S2927</b>	F40CWVX	CW Deluxe 87CRI	20000	2150	48"	30
40	T12	Med. Bi Pin	<b>S6609</b>	F40N	Natural 3400K 86CRI	20000	2100	48"	30
40	T12	Med. Bi Pin	<b>S6611</b>	F40/D30	3000K 70CRI	20000	3200	48"	30
40	T12	Med. Bi Pin	<b>S6614</b>	F40/D830	3000K 80CRI	20000	3300	48"	30
40	T12	Med. Bi Pin	<b>S6612</b>	F40/D35	3500K 70CRI	20000	3200	48"	30
40	T12	Med. Bi Pin	<b>S6615</b>	F40/D835	3500K 80CRI	20000	3300	48"	30
40	T12	Med. Bi Pin	<b>S6613</b>	F40/D41	4100K 70CRI	20000	3200	48"	30
40	T12	Med. Bi Pin	<b>S6616</b>	F40/D841	4100K 80CRI	20000	3300	48"	30
40	T12	Med. Bi Pin	<b>S6610</b>	F40/DSGN50	5000K 90CRI	20000	2200	48"	30
40	T12	Med. Bi Pin	<b>S6608</b>	F40/DX	Day 6500K 88CRI	20000	2180	48"	30
40	T12	Med. Bi Pin	<b>S2928</b>	F40/D865	6500K 80CRI	20000	3000	48"	30
40	T12	Med. Bi Pin	<b>S6668</b>	F40/SUN	Full Spectrum	26000	2100	48"	30



# Fluorescent

# T12 U Bend Tubes

20,000 Hours

## FB34/SS

(Previously FB40T12)

34 Watt

Energy Savers  
Medium Bi Pin Base

6" Leg Spacing

S6680 FB34/Cool White  
S6681 FB34/Warm White

3" Leg Spacing

S6682 FB34/Cool White  
S6690 FB34/Warm White

Designer Series

6" Leg Spacing

S6683 FB34/D30/SS  
S6684 FB34/D35/SS  
S6685 FB34/D41/SS

Packing: 12/Master

Designer series lamps  
equal: 70CRI\*  
Good color rendition  
(Color rendering index\*)



Not Shown Actual Size

## FB40

40 Watt

Standard Wattage  
Medium Bi Pin Base

6" Leg Spacing

S6686 FB40/Daylight Deluxe

Designer Series

S6687 FB40/D30/3000K  
S6688 FB40/D35/3500K  
S6689 FB40/D41/4100K

Packing: 12/Master

### Color Reference Guide

D30/D830 = 3000K Warm White  
D35/D835 = 3500K Neutral  
D41/D841 = 4100K Cool White

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Leg Spacing	Carton
34	T12	Med. Bi Pin	S6680	FB34/CW/6/SS	Cool White	18000	2600	22.5	6"	12
34	T12	Med. Bi Pin	S6681	FB34/WW/6/SS	Warm White	18000	2650	22.5	6"	12
34	T12	Med. Bi Pin	S6683	FB34/D30/6/SS	3000K 70CRI	18000	2730	22.5	6"	12
34	T12	Med. Bi Pin	S6684	FB34/D35/6/SS	3500K 70CRI	18000	2730	22.5	6"	12
34	T12	Med. Bi Pin	S6685	FB34/D41/6/SS	4100K 70CRI	18000	2730	22.5	6"	12
34	T12	Med. Bi Pin	S6682	FB34/CW/3/EW	Cool White	18000	2350	22.5	3"	12
34	T12	Med. Bi Pin	S6690	FB34/WW/3/EW	Warm White	18000	2425	22.5	3"	12
40	T12	Med. Bi Pin	S6686	FB40/DX/6	Daylight Deluxe	18000	2300	22.5	6"	12
40	T12	Med. Bi Pin	S6687	FB40/D30/6	3000K 70CRI	18000	3050	22.5	6"	12
40	T12	Med. Bi Pin	S6688	FB40/D35/6	3500K 70CRI	18000	3050	22.5	6"	12
40	T12	Med. Bi Pin	S6689	FB40/D41/6	4100K 70CRI	18000	3050	22.5	6"	12

# Fluorescent *Slimline* Tubes

## Slimline Instant Start Lamps



Not Shown Actual Size

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
25	T6	Single Pin	S6471	F42T6/CW	Cool White	7500	1750	42"	24
25	T6	Single Pin	S2929	F42T6/D35	3500K 70CRI	7500	1830	42"	24
25	T6	Single Pin	S6470	F42T6/WW	Warm White	7500	1825	42"	24
38	T6	Single Pin	S6475	F64T6/CW	Cool White	7500	2800	64"	24
38	T6	Single Pin	S6473	F64T6/WW	Warm White	7500	2900	64"	24
38	T8	Single Pin	S6478	F72T8/CW	Cool White	7500	3050	72"	24
38	T8	Single Pin	S6477	F72T8/WW	Warm White	7500	3100	72"	24
38	T8	Single Pin	S6476	F72T8/D	Daylight	7500	2600	72"	24
38	T8	Single Pin	S2930	F96T8/CW	Cool White	7500	4000	96"	24
38	T8	Single Pin	S2931	F96T8/D	Daylight	7500	3550	96"	24
24	T12	Single Pin	S6469	F24T12/CW	Cool White	7500	1150	24"	30
30	T12	Single Pin	S6472	F36T12/CW	Cool White	7500	1970	36"	30
39	T12	Single Pin	S6660	F48T12/CW	Cool White	9000	2875	48"	30
39	T12	Single Pin	S6481	F48T12/D	Daylight	9000	2450	48"	30
50	T12	Single Pin	S6661	F60T12/CW	Cool White	12000	3700	60"	30
50	T12	Single Pin	S6483	F60T12/D	Daylight	12000	3000	60"	30
52	T12	Single Pin	S6662	F64T12/CW	Cool White	12000	3900	64"	30
52	T12	Single Pin	S6485	F64T12/D	Daylight	12000	3300	64"	30
55	T12	Single Pin	S6630	F72T12/CW	Cool White	12000	4500	72"	15
55	T12	Single Pin	S6631	F72T12/WW	Warm White	12000	4550	72"	15
55	T12	Single Pin	S6632	F72T12/D	Daylight	12000	3800	72"	15
70	T12	Single Pin	S6663	F84T12/CW	Cool White	12000	5300	84"	15

# Fluorescent *Slimline* Tubes



## F96T12

Full Wattage  
Single Pin Base

**S6650** F96T12/Daylight Deluxe

**S6651** F96T12/Design 50

Designer Series

**S6652** F96T12/D30

**S6653** F96T12/D35

**S6654** F96T12/D41

Designer 800 Series

**S6655** F96T12/D830

**S6656** F96T12/D835

**S6657** F96T12/D841

**S2932** F96T12/D865

Packing: 15/Master

**Color Reference Guide**  
D30/D830 = 3000K Warm White  
D35/D835 = 3500K Neutral  
D41/D841 = 4100K Cool White

Not Shown Actual Size



## F96T12/SS

Energy Savers  
Single Pin Base

**S6640** F96T12/Cool White/SS

**S6641** F96T12/Warm White/SS

Designer Series

**S6642** F96T12/D30/SS

**S6643** F96T12/D35/SS

**S6644** F96T12/D41/SS

Designer 800 Series

**S6645** F96T12/D830/SS

**S6646** F96T12/D835/SS

**S6647** F96T12/D841/SS

700 Series lamps equal: 70CRI\*  
Good color rendition

800 Series lamps equal: 80CRI\*  
Superior color rendition

(Color rendering index\*)

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
60	T12	Single Pin	<b>S6640</b>	F96T12/CW/SS	Cool White	12000	5300	96"	15
60	T12	Single Pin	<b>S6641</b>	F96T12/WW/SS	Warm White	12000	5500	96"	15
60	T12	Single Pin	<b>S6642</b>	F96T12/D30/SS	3000K 70CRI	12000	5600	96"	15
60	T12	Single Pin	<b>S6645</b>	F96T12/D830/SS	3000K 80CRI	12000	5800	96"	15
60	T12	Single Pin	<b>S6643</b>	F96T12/D35/SS	3500K 70CRI	12000	5600	96"	15
60	T12	Single Pin	<b>S6646</b>	F96T12/D835/SS	3500K 80CRI	12000	5800	96"	15
60	T12	Single Pin	<b>S6644</b>	F96T12/D41/SS	4100K 70CRI	12000	5600	96"	15
60	T12	Single Pin	<b>S6647</b>	F96T12/D841/SS	4100K 80CRI	12000	5800	96"	15
75	T12	Single Pin	<b>S6652</b>	F96T12/D30	3000K 70CRI	12000	6420	96"	15
75	T12	Single Pin	<b>S6655</b>	F96T12/D830	3000K 80CRI	12000	6550	96"	15
75	T12	Single Pin	<b>S6653</b>	F96T12/D35	3500K 70CRI	12000	6420	96"	15
75	T12	Single Pin	<b>S6656</b>	F96T12/D835	3500K 80CRI	12000	6550	96"	15
75	T12	Single Pin	<b>S6654</b>	F96T12/D41	4100K 70CRI	12000	6420	96"	15
75	T12	Single Pin	<b>S6657</b>	F96T12/D841	4100K 80CRI	12000	6550	96"	15
75	T12	Single Pin	<b>S6651</b>	F96T12/D50	5000K 90CRI	12000	4400	96"	15
75	T12	Single Pin	<b>S6650</b>	F96T12/DX	Daylight Deluxe	12000	4310	96"	15
75	T12	Single Pin	<b>S2932</b>	F96T12/D865	6500K 80CRI	12000	6000	96"	15

fluorescent lamps

# Fluorescent *HO T12* Tubes



Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Inner Pack
25	T12	Recessed D.C.	S2933	F18T12/CW/HO	Cool White	9000	1100	18"	30
25	T12	Recessed D.C.	S2934	F18T12/DSGN50/HO	5000K 90CRI	9000	850	18"	30
35	T12	Recessed D.C.	S6449	F24T12/CW/HO	Cool White	9000	1650	24"	30
35	T12	Recessed D.C.	S2935	F24T12/DSGN50/HO	5000K 90CRI	9000	1200	24"	30
35	T12	Recessed D.C.	S6450	F24T12/D/HO	Daylight	9000	1400	24"	30
42	T12	Recessed D.C.	S6451	F30T12/CW/HO	Cool White	9000	2250	30"	30
45	T12	Recessed D.C.	S6452	F36T12/CW/HO	Cool White	9000	2850	36"	30
45	T12	Recessed D.C.	S2936	F36T12/DSGN50/HO	5000K 90CRI	9000	2100	36"	30
45	T12	Recessed D.C.	S2937	F36T12/D/HO	Daylight	9000	2500	36"	30
55	T12	Recessed D.C.	S6453	F42T12/CW/HO	Cool White	9000	3400	42"	30
55	T12	Recessed D.C.	S2938	F42T12/DSGN50/HO	5000K 90CRI	9000	2550	42"	30
55	T12	Recessed D.C.	S6454	F42T12/D/HO	Daylight	9000	3050	42"	30
60	T12	Recessed D.C.	S6670	F48T12/CW/HO	Cool White	12000	4050	48"	30
60	T12	Recessed D.C.	S2939	F48T12/DSGN50/HO	5000K 90CRI	12000	3050	48"	30
60	T12	Recessed D.C.	S2940	F48T12/D/HO	Daylight	12000	3600	48"	30
75	T12	Recessed D.C.	S6671	F60T12/CW/HO	Cool White	12000	5200	60"	30
75	T12	Recessed D.C.	S2941	F60T12/DSGN50/HO	5000K 90CRI	12000	3850	60"	30
75	T12	Recessed D.C.	S6457	F60T12/D/HO	Daylight	12000	4600	60"	30
80	T12	Recessed D.C.	S6672	F64T12/CW/HO	Cool White	12000	5750	64"	30
80	T12	Recessed D.C.	S2942	F64T12/DSGN50/HO	5000K 90CRI	12000	4200	64"	30
80	T12	Recessed D.C.	S6458	F64T12/D/HO	Daylight	12000	4900	64"	30

# Fluorescent *HO/VHO T12* Tubes



Not Shown Actual Size

fluorescent lamps

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
<b>High Output (800 MA)</b>									
85	T12	Recessed D.C.	<b>S6673</b>	F72T12/CW/HO	Cool White	12000	6250	72"	15
85	T12	Recessed D.C.	<b>S2943</b>	F72T12/DSGN50/HO	5000K 90CRI	12000	4600	72"	15
85	T12	Recessed D.C.	<b>S6460</b>	F72T12/D/HO	Daylight	12000	5550	72"	15
85	T12	Recessed D.C.	<b>S2944</b>	F72T12/D35/HO	3500K 70CRI	12000	6650	72"	15
100	T12	Recessed D.C.	<b>S6674</b>	F84T12/CW/HO	Cool White	12000	7550	84"	15
100	T12	Recessed D.C.	<b>S2945</b>	F84T12/DSGN50/HO	5000K 90CRI	12000	5600	84"	15
100	T12	Recessed D.C.	<b>S6461</b>	F84T12/D/HO	Daylight	12000	6700	84"	15
95	T12	Recessed D.C.	<b>S6675</b>	F96T12/CW/HO/SS	Cool White	12000	8000	96"	15
110	T12	Recessed D.C.	<b>S6676</b>	F96T12/CW/HO-COLD	Cool White	12000	8600	96"	15
110	T12	Recessed D.C.	<b>S2946</b>	F96T12/DSGN50/HO	5000K 90CRI	12000	6450	96"	15
110	T12	Recessed D.C.	<b>S6462</b>	F96T12/D/HO-COLD	Daylight	12000	7600	96"	15
110	T12	Recessed D.C.	<b>S2947</b>	F96T12/D30/HO	3000K 70CRI	12000	9050	96"	15
110	T12	Recessed D.C.	<b>S2948</b>	F96T12/D35/HO	3500K 70CRI	12000	9050	96"	15
110	T12	Recessed D.C.	<b>S2949</b>	F96T12/D41/HO	4100K 70CRI	12000	9050	96"	15
<b>Very High Output (1500 MA)</b>									
115	T12	Recessed D.C.	<b>S6463</b>	F48T12/CW/VHO	Cool White	10000	6600	48"	30
135	T12	Recessed D.C.	<b>S6465</b>	F60T12/CW/VHO	Cool White	10000	8700	60"	30
160	T12	Recessed D.C.	<b>S6466</b>	F72T12/CW/VHO	Cool White	10000	10600	72"	15
195	T12	Recessed D.C.	<b>S6467</b>	F96T12/CW/VHO/SS	Cool White	10000	13000	96"	15
215	T12	Recessed D.C.	<b>S6677</b>	F96T12/CW/VHO	Cool White	10000	14000	96"	15

# Fluorescent T9 Circline Tubes



fluorescent lamps



### FC6T9/6.5"

20 Watt  
4 Pin Base  
S6509 Cool White  
S2950 Warm White

### FC8T9/8"

22 Watt  
4 Pin Base  
S6500 Cool White  
S6501 Daylight  
S6502 Warm White

### FC12T9/12"

32 Watt  
4 Pin Base  
S6503 Cool White  
S6504 Daylight  
S6505 Warm White

### FC16T9/16"

40 Watt  
4 Pin Base  
S6506 Cool White  
S2953 Daylight  
S2954 Warm White

Packing: 12/Master

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Diameter	Carton
20	T9	4 Pin	S6509	FC6T9/CW	Cool White	8000	750	6.5"	12
20	T9	4 Pin	S2950	FC6T9/WW	Warm White	8000	800	6.5"	12
22	T9	4 Pin	S6500	FC8T9/CW	Cool White	11000	1050	8"	12
22	T9	4 Pin	S6501	FC8T9/D	Daylight	11000	900	8"	12
22	T9	4 Pin	S6502	FC8T9/WW	Warm White	11000	1050	8"	12
32	T9	4 Pin	S6503	FC12T9/CW	Cool White	15000	1925	12"	12
32	T9	4 Pin	S6504	FC12T9/D	Daylight	15000	1650	12"	12
32	T9	4 Pin	S6505	FC12T9/WW	Warm White	15000	1950	12"	12
40	T9	4 Pin	S6506	FC16T9/CW	Cool White	18000	2750	16"	12
40	T9	4 Pin	S2953	FC16T9/D	Daylight	18000	2350	16"	12
40	T9	4 Pin	S2954	FC16T9/WW	Warm White	18000	2800	16"	12

# Fluorescent

# Circline T5 Tubes

Tri-Phosphor — Electronic Ballast

12,000 Hours



Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Color/CRI	Avg. Rated Hours	Initial Lumens	Diameter	Carton
22	T5	2GX13	S2955	FPC22/830	3000K 82CRI	12000	1800	9"	12
22	T5	2GX13	S2956	FPC22/835	3500K 82CRI	12000	1800	9"	12
22	T5	2GX13	S2957	FPC22/841	4100K 82CRI	12000	1800	9"	12
40	T5	2GX13	S2958	FPC40/830	3000K 82CRI	12000	3200	12"	12
40	T5	2GX13	S2959	FPC40/835	3500K 82CRI	12000	3200	12"	12
40	T5	2GX13	S2960	FPC40/841	4100K 82CRI	12000	3200	12"	12
55	T5	2GX13	S2961	FPC55/830/HO	3000K 82CRI	12000	4000	12"	12
55	T5	2GX13	S2962	FPC55/835/HO	3500K 82CRI	12000	4000	12"	12
55	T5	2GX13	S2963	FPC55/841/HO	4100K 82CRI	12000	4000	12"	12

fluorescent lamps

# Shatter Proof Fluorescent Lamps



T6

**Single Pin Base**  
**S6591** F42T6/CW/TF  
**S6692** F64T6/CW/TF  
 Packing: 24/Master



T8

**Electronic**  
**Medium Bi Pin Base**  
**S6583** FO17/741/TF  
**S6584** FO25/741/TF  
**S6585** FO32/741/TF  
 Packing: 30/Master



T8

**U-Bend**  
**Medium Bi Pin Base**  
**S6594** FBO32/741/6/TF  
 Packing: 16/Master

**Satco Shatter Proof Lamps** feature a special **Kenlon®** coating which effectively contains glass particles should the lamp break. These lamps are perfect in use food storage

preparation, display and sorting tables, hospitals, restaurants and recreation facilities. Special orders are available for large quantities on specific lamp types.

## Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
25	T6	Single Pin	<b>S6591</b>	F42T6/CW/TF	Coated	7500	1750	42"	24
38	T6	Single Pin	<b>S6592</b>	F64T6/CW/TF	Coated	7500	2800	64"	24
17	T8	Med. Bi-Pin	<b>S6583</b>	FO17/741/TF	Coated	20000	1300	24"	30
25	T8	Med. Bi-Pin	<b>S6584</b>	FO25/741/TF	Coated	20000	2025	36"	30
32	T8	Med. Bi-Pin	<b>S6585</b>	FO32/741/TF	Coated	20000	2750	48"	30
32	T8	Med. Bi-Pin	<b>S6594</b>	FBO32/741/6/TF	Coated	20000	2750	22.5"	16



# Shatter Proof Fluorescent Lamps



T12

## U-Bend Cool White

**S6593** FB34CW/6/SS/TF  
Packing: 12/Master



T12 Cool White

## Medium Bi-Pin Base

**S6579** F20T12/CW/TF  
**S6580** F30T12/CW/TF  
**S6581** F34/CW/SS/TF  
Packing: 30/Master

## Single Pin Base

**S6586** F48T12/CW/TF  
Packing: 30/Master  
**S6582** F96T12/CW/SS/TF  
Packing: 15/Master

## Recessed Double Contact Base

**S6587** F48T12/CW/HO/TF  
**S6595** F48T12/CW/VHO/TF  
Packing: 30/Master  
**S6588** F96T12/CW/HO/SS/TF  
**S6589** F96T12/CW/HO/CT/TF  
**S6590** F96T12/CW/VHO/TF  
Packing: 15/Master

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
20	T12	Med. Bi- Pin	<b>S6579</b>	F20T12/CW/TF	Coated	9000	1220	24"	30
30	T12	Med. Bi- Pin	<b>S6580</b>	F30T12/CW/TF	Coated	18000	2200	36"	30
34	T12	Med. Bi- Pin	<b>S6581</b>	F34T12/CW/SS/TF	Coated	20000	2650	48"	30
39	T12	Single Pin	<b>S6586</b>	F48T12/CW/TF	Coated	9000	2875	48"	30
60	T12	Single Pin	<b>S6587</b>	F48T12/CW/HO/TF	Coated	20000	4050	48"	30
115	T12	Single Pin	<b>S6595</b>	F48T12/CW/VHO/LT/TF	Coated	20000	7400	48"	30
60	T12	Single Pin	<b>S6582</b>	F96T12/CW/SS/TF	Coated	12000	5300	96"	15
95	T12	Rec. D.C.	<b>S6588</b>	F96T12/CW/HO/SS/TF	Coated	12000	8000	96"	15
110	T12	Rec. D.C.	<b>S6589</b>	F96T12/CW/HO/COLD TEMP/TF	Coated	12000	8600	96"	15
215	T12	Rec. D.C.	<b>S6590</b>	F96T12/CW/VHO/TF	Coated	10000	14000	96"	15
34	T12	Med. Bi- Pin	<b>S6593</b>	FB34/CW/6/SS/TF	Coated	18000	2600	22.5"	12

fluorescent lamps

# Compact Fluorescent

## Twin Tubes **SATCO**<sup>®</sup>

Not Shown Actual Size

**10,000 Hours**



**CFS5**

5 Watt  
G23 Base

**S6300** CFS5W/827

**S6301** CFS5W/841

Packing:  
50/Master,  
Individually Boxed



**CFS7**

7 Watt  
G23 Base

**S6302** CFS7W/827

**S6303** CFS7W/835

**S6304** CFS7W/841

**S6305** CFS7W/850

Packing:  
50/Master,  
Individually Boxed



**CFS9**

9 Watt  
G23 Base

**S6306** CFS9W/827

**S6307** CFS9W/835

**S6308** CFS9W/841

**S6309** CFS9W/850

Packing:  
50/Master,  
Individually Boxed



**CFS13**

13 Watt  
GX23 Base

**S6310** CFS13W/827

**S6380** CFS13W/830

**S6311** CFS13W/835

**S6312** CFS13W/841

**S6313** CFS13W/850

Packing:  
50/Master,  
Individually Boxed

### SATCO COMPACT FLUORESCENT LAMPS QUALITY • VALUE • PERFORMANCE

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Pack. Type	Mst.Ctn./Inner Pack
5	T4	G23	<b>S6300</b>	CFS5W/827	2700K 82CRI	10000	230	4.2"	Box	50/5
5	T4	G23	<b>S6301</b>	CFS5W/841	4100K 82CRI	10000	230	4.2"	Box	50/5
7	T4	G23	<b>S6302</b>	CFS7W/827	2700K 82CRI	10000	400	5.3"	Box	50/5
7	T4	G23	<b>S6303</b>	CFS7W/835	3500K 82CRI	10000	400	5.3"	Box	50/5
7	T4	G23	<b>S6304</b>	CFS7W/841	4100K 82CRI	10000	400	5.3"	Box	50/5
7	T4	G23	<b>S6305</b>	CFS7W/850	5000K 82CRI	10000	400	5.3"	Box	50/5
9	T4	G23	<b>S6306</b>	CFS9W/827	2700K 82CRI	10000	580	6.5"	Box	50/5
9	T4	G23	<b>S6307</b>	CFS9W/835	3500K 82CRI	10000	580	6.5"	Box	50/5
9	T4	G23	<b>S6308</b>	CFS9W/841	4100K 82CRI	10000	580	6.5"	Box	50/5
9	T4	G23	<b>S6309</b>	CFS9W/850	5000K 82CRI	10000	580	6.5"	Box	50/5
13	T4	GX23	<b>S6310</b>	CFS13W/827	2700K 82CRI	10000	800	7.1"	Box	50/5
13	T4	GX23	<b>S6380</b>	CFS13W/830	3000K 82CRI	10000	800	7.1"	Box	50/5
13	T4	GX23	<b>S6311</b>	CFS13W/835	3500K 82CRI	10000	800	7.1"	Box	50/5
13	T4	GX23	<b>S6312</b>	CFS13W/841	4100K 82CRI	10000	800	7.1"	Box	50/5
13	T4	GX23	<b>S6313</b>	CFS13W/850	5000K 82CRI	10000	800	7.1"	Box	50/5

fluorescent lamps



# Compact Fluorescent

10000 Hours

## Two Pin Quad Tubes

Not Shown  
Actual Size



**CFD26**

**26 Watt**  
G24d-3 2 Pin Base  
**S6325** CFD26W/827  
**S6326** CFD26W/830  
**S6327** CFD26W/835  
**S6328** CFD26W/841

Packing:  
50/Master,  
Individually Boxed



**CFD18**

**18 Watt**  
G24d-2 2 Pin Base  
**S6321** CFD18W/827  
**S6322** CFD18W/830  
**S6323** CFD18W/835  
**S6324** CFD18W/841

Packing:  
50/Master,  
Individually Boxed



**CFD13**

**13 Watt**  
GX23-2 2 Pin Base  
**S6317** CFD13W/827  
**S6318** CFD13W/830  
**S6319** CFD13W/835  
**S6320** CFD13W/841

Packing:  
50/Master,  
Individually Boxed



**CFD9**

**9 Watt**  
G23-2 2 Pin Base  
**S6314** CFD9W/827  
**S6315** CFD9W/830  
**S6316** CFD9W/835

Packing:  
50/Master,  
Individually Boxed

fluorescent lamps

### SATCO COMPACT FLUORESCENT LAMPS QUALITY • VALUE • PERFORMANCE

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Mst.Ctn./ Inner Pack
9	T4	G23-2	<b>S6314</b>	CFD9W/827	2700K 82CRI	10000	525	4.3"	50/5
9	T4	G23-2	<b>S6315</b>	CFD9W/830	3000K 82CRI	10000	525	4.3"	50/5
9	T4	G23-2	<b>S6316</b>	CFD9W/835	3500K 82CRI	10000	525	4.3"	50/5
13	T4	GX23-2	<b>S6317</b>	CFD13W/827	2700K 82CRI	10000	780	4.6"	50/5
13	T4	GX23-2	<b>S6318</b>	CFD13W/830	3000K 82CRI	10000	780	4.6"	50/5
13	T4	GX23-2	<b>S6319</b>	CFD13W/835	3500K 82CRI	10000	780	4.6"	50/5
13	T4	GX23-2	<b>S6320</b>	CFD13W/841	4100K 82CRI	10000	780	4.6"	50/5
18	T4	G24D-2	<b>S6321</b>	CFD18W/827	2700K 82CRI	10000	1250	6.0"	50/5
18	T4	G24D-2	<b>S6322</b>	CFD18W/830	3000K 82CRI	10000	1250	6.0"	50/5
18	T4	G24D-2	<b>S6323</b>	CFD18W/835	3500K 82CRI	10000	1250	6.0"	50/5
18	T4	G24D-2	<b>S6324</b>	CFD18W/841	4100K 82CRI	10000	1250	6.0"	50/5
26	T4	G24D-3	<b>S6325</b>	CFD26W/827	2700K 82CRI	10000	1825	6.8"	50/5
26	T4	G24D-3	<b>S6326</b>	CFD26W/830	3000K 82CRI	10000	1825	6.8"	50/5
26	T4	G24D-3	<b>S6327</b>	CFD26W/835	3500K 82CRI	10000	1825	6.8"	50/5
26	T4	G24D-3	<b>S6328</b>	CFD26W/841	4100K 82CRI	10000	1825	6.8"	50/5

# Compact Fluorescent *Four Pin* Electronic



Not Shown Actual Size



**CFD13W/4P**

**13 Watt**  
G24q-1 4 Pin Base

- S6329** CFD13W/4P/827
- S6330** CFD13W/4P/830
- S6331** CFD13W/4P/835
- S6332** CFD13W/4P/841

Packing:  
50/Master,  
Individually Boxed



**CFD18W/4P**

**18 Watt**  
G24q-2 4 Pin Base

- S6333** CFD18W/4P/827
- S6334** CFD18W/4P/830
- S6335** CFD18W/4P/835
- S6336** CFD18W/4P/841

Packing:  
50/Master,  
Individually Boxed



**CFD26W/4P**

**26 Watt**  
G24q-3 4 Pin Base

- S6337** CFD26W/4P/827
- S6338** CFD26W/4P/830
- S6339** CFD26W/4P/835
- S6340** CFD26W/4P/841

Packing:  
50/Master,  
Individually Boxed

## SATCO COMPACT FLUORESCENT LAMPS QUALITY • VALUE • PERFORMANCE

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Mst. Ctn./ Inner Pack.
13	T4	G24q-1	<b>S6329</b>	CFD13W/4P/827	2700K 82CRI	12000	900	5.2"	50/5
13	T4	G24q-1	<b>S6330</b>	CFD13W/4P/830	3000K 82CRI	12000	900	5.2"	50/5
13	T4	G24q-1	<b>S6331</b>	CFD13W/4P/835	3500K 82CRI	12000	900	5.2"	50/5
13	T4	G24q-1	<b>S6332</b>	CFD13W/4P/841	4100K 82CRI	12000	900	5.2"	50/5
18	T4	G24q-2	<b>S6333</b>	CFD18W/4P/827	2700K 82CRI	12000	1250	5.8"	50/5
18	T4	G24q-2	<b>S6334</b>	CFD18W/4P/830	3000K 82CRI	12000	1250	5.8"	50/5
18	T4	G24q-2	<b>S6335</b>	CFD18W/4P/835	3500K 82CRI	12000	1250	5.8"	50/5
18	T4	G24q-2	<b>S6336</b>	CFD18W/4P/841	4100K 82CRI	12000	1250	5.8"	50/5
26	T4	G24q-3	<b>S6337</b>	CFD26W/4P/827	2700K 82CRI	12000	1825	6.5"	50/5
26	T4	G24q-3	<b>S6338</b>	CFD26W/4P/830	3000K 82CRI	12000	1825	6.5"	50/5
26	T4	G24q-3	<b>S6339</b>	CFD26W/4P/835	3500K 82CRI	12000	1825	6.5"	50/5
26	T4	G24q-3	<b>S6340</b>	CFD26W/4P/841	4100K 82CRI	12000	1825	6.5"	50/5

# Compact Fluorescent Four Pin Electronic Triple Tube



### CFT13W/4P

13 Watt  
GX24q-1 4 Pin Base  
**S6496** CFT13W/4P/830  
**S6497** CFT13W/4P/835  
**S6498** CFT13W/4P/841

### CFT18W/4P

18 Watt  
GX24q-2 4 Pin Base  
**S6342** CFT18W/4P/830  
**S6343** CFT18W/4P/835  
**S6344** CFT18W/4P/841

### CFT26W/4P

26 Watt  
GX24q-3 4 Pin Base  
**S6346** CFT26W/4P/830  
**S6347** CFT26W/4P/835  
**S6348** CFT26W/4P/841

### CFT32W/4P

32 Watt  
GX24q-3 4 Pin Base  
**S6350** CFT32W/4P/830  
**S6351** CFT32W/4P/835  
**S6352** CFT32W/4P/841

### CFT42W/4P

42 Watt  
GX24q-4 4 Pin Base  
**S6354** CFT42W/4P/830  
**S6355** CFT42W/4P/835  
**S6356** CFT42W/4P/841

Not Shown  
Actual Size

Packing:  
50/Master,  
Individually Boxed

**SATCO COMPACT FLUORESCENT LAMPS**  
**QUALITY • VALUE • PERFORMANCE**

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Pack. Type	Mst.Ctn./ Inner Pack
13	T4	GX24Q-1	<b>S6496</b>	CFT13W/4P/830	3000K 82CRI	12000	900	4.2"	Box	50/5
13	T4	GX24Q-1	<b>S6497</b>	CFT13W/4P/835	3500K 82CRI	12000	900	4.2"	Box	50/5
13	T4	GX24Q-1	<b>S6498</b>	CFT13W/4P/841	4100K 82CRI	12000	900	4.2"	Box	50/5
18	T4	GX24q-2	<b>S6342</b>	CFT18W/4P/830	3000K 82CRI	12000	1200	4.4"	Box	50/5
18	T4	GX24q-2	<b>S6343</b>	CFT18W/4P/835	3500K 82CRI	12000	1200	4.4"	Box	50/5
18	T4	GX24q-2	<b>S6344</b>	CFT18W/4P/841	4100K 82CRI	12000	1200	4.4"	Box	50/5
26	T4	GX24q-3	<b>S6346</b>	CFT26W/4P/830	3000K 82CRI	12000	1800	5.0"	Box	50/5
26	T4	GX24q-3	<b>S6347</b>	CFT26W/4P/835	3500K 82CRI	12000	1800	5.0"	Box	50/5
26	T4	GX24q-3	<b>S6348</b>	CFT26W/4P/841	4100K 82CRI	12000	1800	5.0"	Box	50/5
32	T4	GX24q-3	<b>S6350</b>	CFT32W/4P/830	3000K 82CRI	12000	2400	5.6"	Box	50/5
32	T4	GX24q-3	<b>S6351</b>	CFT32W/4P/835	3500K 82CRI	12000	2400	5.6"	Box	50/5
32	T4	GX24q-3	<b>S6352</b>	CFT32W/4P/841	4100K 82CRI	12000	2400	5.6"	Box	50/5
42	T4	GX24q-4	<b>S6354</b>	CFT42W/4P/830	3000K 82CRI	12000	3200	6.5"	Box	50/5
42	T4	GX24q-4	<b>S6355</b>	CFT42W/4P/835	3500K 82CRI	12000	3200	6.5"	Box	50/5
42	T4	GX24q-4	<b>S6356</b>	CFT42W/4P/841	4100K 82CRI	12000	3200	6.5"	Box	50/5

# Compact Fluorescent *Twin* Tubes

Not Shown Actual Size

**10,000 Hours**



**CF5DS**

**5 Watt  
G23 Base**

**S6700** CF5DS/827  
**S6701** CF5DS/841

Packing:  
50/Master,  
Individually Boxed



**CF7DS**

**7 Watt  
G23 Base**

**S6702** CF7DS/827  
**S6703** CF7DS/835  
**S6704** CF7DS/841  
**S6705** CF7DS/850

Packing:  
50/Master,  
Individually Boxed



**CF9DS**

**9 Watt  
G23 Base**

**S6706** CF9DS/827  
**S6707** CF9DS/835  
**S6708** CF9DS/841  
**S6709** CF9DS/850

Packing:  
50/Master,  
Individually Boxed



**CF13DS**

**13 Watt  
GX23 Base**

**S6710** CF13DS/827  
**S6780** CF13DS/830  
**S6711** CF13DS/835  
**S6712** CF13DS/841  
**S6713** CF13DS/850

Packing:  
50/Master,  
Individually Boxed

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Pack. Type	Mst. Ctn./ Inner Pack
5	T4	G23	<b>S6700</b>	CF5DS/827	2700K 82CRI	10000	230	4.2"	Box	50
5	T4	G23	<b>S6701</b>	CF5DS/841	4100K 82CRI	10000	230	4.2"	Box	50
7	T4	G23	<b>S6702</b>	CF7DS/827	2700K 82CRI	10000	400	5.3"	Box	50
7	T4	G23	<b>S6703</b>	CF7DS/835	3500K 82CRI	10000	400	5.3"	Box	50
7	T4	G23	<b>S6704</b>	CF7DS/841	4100K 82CRI	10000	400	5.3"	Box	50
7	T4	G23	<b>S6705</b>	CF7DS/850	5000K 82CRI	10000	400	5.3"	Box	50
9	T4	G23	<b>S6706</b>	CF9DS/827	2700K 82CRI	10000	580	6.5"	Box	50
9	T4	G23	<b>S6707</b>	CF9DS/835	3500K 82CRI	10000	580	6.5"	Box	50
9	T4	G23	<b>S6708</b>	CF9DS/841	4100K 82CRI	10000	580	6.5"	Box	50
9	T4	G23	<b>S6709</b>	CF9DS/850	5000K 82CRI	10000	580	6.5"	Box	50
13	T4	GX23	<b>S6710</b>	CF13DS/827	2700K 82CRI	10000	800	7.1"	Box	50
13	T4	GX23	<b>S6780</b>	CF13DS/830	3000K 82CRI	10000	800	7.1"	Box	50
13	T4	GX23	<b>S6711</b>	CF13DS/835	3500K 82CRI	10000	800	7.1"	Box	50
13	T4	GX23	<b>S6712</b>	CF13DS/841	4100K 82CRI	10000	800	7.1"	Box	50
13	T4	GX23	<b>S6713</b>	CF13DS/850	5000K 82CRI	10000	800	7.1"	Box	50

# Compact Fluorescent *Four Pin* Tubes

10,000 Hours

Not Shown Actual Size



**CF13DS/E**

**13 Watt**

2G7 4 Pin Base

**S6417** CF13DS/E/827

**S6418** CF13DS/E/830

**S6419** CF13DS/E/841

Packing:

50/Master,

Individually Boxed



**CF9DS/E**

**9 Watt**

2G7 4 Pin Base

**S6415** CF9DS/E/827

**S6416** CF9DS/E/841

Packing:

50/Master,

Individually Boxed



**CF7DS/E**

**7 Watt**

2G7 4 Pin Base

**S6413** CF7DS/E/827

**S6414** CF7DS/E/841

Packing:

50/Master,

Individually Boxed



**CF5DS/E**

**5 Watt**

2G7 4 Pin Base

**S6411** CF5DS/E/827

**S6412** CF5DS/E/841

Packing:

50/Master,

Individually Boxed

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Pack. Type	Mst.Ctn./ Inner Pack
5	T4	2G7	<b>S6411</b>	CF5DS/E/827	2700K 82CRI	10000	230	3.4"	Box	50
5	T4	2G7	<b>S6412</b>	CF5DS/E/841	4100K 82CRI	10000	230	3.4"	Box	50
7	T4	2G7	<b>S6413</b>	CF7DS/E/827	2700K 82CRI	10000	400	4.5"	Box	50
7	T4	2G7	<b>S6414</b>	CF7DS/E/841	4100K 82CRI	10000	400	4.5"	Box	50
9	T4	2G7	<b>S6415</b>	CF9DS/E/827	2700K 82CRI	10000	580	5.7"	Box	50
9	T4	2G7	<b>S6416</b>	CF9DS/E/841	4100K 82CRI	10000	580	5.7"	Box	50
13	T4	2GX7	<b>S6417</b>	CF13DS/E/827	2700K 82CRI	10000	800	6.2"	Box	50
13	T4	2GX7	<b>S6418</b>	CF13DS/E/830	3000K 82CRI	10000	800	6.2"	Box	50
13	T4	2GX7	<b>S6419</b>	CF13DS/E/841	4100K 82CRI	10000	800	6.2"	Box	50

fluorescent lamps

# Compact Fluorescent

## Two Pin *10,000 Hours* Quad Tubes

Not Shown  
Actual Size



**CF9DD**

**9 Watt**

G23-2 2 Pin Base

**S6714** CF9DD/827

**S6715** CF9DD/830

**S6716** CF9DD/835

Packing:  
50/Master,  
Individually Boxed



**CF13DD**

**13 Watt**

GX23-2 2 Pin Base

**S6717** CF13DD/827

**S6718** CF13DD/830

**S6719** CF13DD/835

**S6720** CF13DD/841

Packing:  
50/Master,  
Individually Boxed



**CF18DD**

**18 Watt**

G24d-2 2 Pin Base

**S6721** CF18DD/827

**S6722** CF18DD/830

**S6723** CF18DD/835

**S6724** CF18DD/841

Packing:  
50/Master,  
Individually Boxed



**CF26DD**

**26 Watt**

G24d-3 2 Pin Base

**S6725** CF26DD/827

**S6726** CF26DD/830

**S6727** CF26DD/835

**S6728** CF26DD/841

Packing:  
50/Master,  
Individually Boxed

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
9	T4	G23-2	<b>S6714</b>	CF9DD/827	2700K 82CRI	10000	525	4.3"	50
9	T4	G23-2	<b>S6715</b>	CF9DD/830	3000K 82CRI	10000	525	4.3"	50
9	T4	G23-2	<b>S6716</b>	CF9DD/835	3500K 82CRI	10000	525	4.3"	50
13	T4	GX23-2	<b>S6717</b>	CF13DD/827	2700K 82CRI	10000	780	4.6"	50
13	T4	GX23-2	<b>S6718</b>	CF13DD/830	3000K 82CRI	10000	780	4.6"	50
13	T4	GX23-2	<b>S6719</b>	CF13DD/835	3500K 82CRI	10000	780	4.6"	50
13	T4	GX23-2	<b>S6720</b>	CF13DD/841	4100K 82CRI	10000	780	4.6"	50
18	T4	G24D-2	<b>S6721</b>	CF18DD/827	2700K 82CRI	10000	1250	6.0"	50
18	T4	G24D-2	<b>S6722</b>	CF18DD/830	3000K 82CRI	10000	1250	6.0"	50
18	T4	G24D-2	<b>S6723</b>	CF18DD/835	3500K 82CRI	10000	1250	6.0"	50
18	T4	G24D-2	<b>S6724</b>	CF18DD/841	4100K 82CRI	10000	1250	6.0"	50
26	T4	G24D-3	<b>S6725</b>	CF26DD/827	2700K 82CRI	10000	1825	6.8"	50
26	T4	G24D-3	<b>S6726</b>	CF26DD/830	3000K 82CRI	10000	1825	6.8"	50
26	T4	G24D-3	<b>S6727</b>	CF26DD/835	3500K 82CRI	10000	1825	6.8"	50
26	T4	G24D-3	<b>S6728</b>	CF26DD/841	4100K 82CRI	10000	1825	6.8"	50



# Compact Fluorescent *Four Pin* Electronic

Not Shown Actual Size



**CF26DD/E**

**26 Watt**

G24q-3 4 Pin Base

- S6737** CF26DD/E/827
- S6738** CF26DD/E/830
- S6739** CF26DD/E/835
- S6740** CF26DD/E/841

Packing:  
50/Master,  
Individually Boxed



**CF18DD/E**

**18 Watt**

G24q-2 4 Pin Base

- S6733** CF18DD/E/827
- S6734** CF18DD/E/830
- S6735** CF18DD/E/835
- S6736** CF18DD/E/841

Packing:  
50/Master,  
Individually Boxed



**CF13DD/E**

**13 Watt**

G24q-1 4 Pin Base

- S6729** CF13DD/E/827
- S6730** CF13DD/E/830
- S6731** CF13DD/E/835
- S6732** CF13DD/E/841

Packing:  
50/Master,  
Individually Boxed

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
13	T4	G24q-1	<b>S6729</b>	CF13DD/E/827	2700K 82CRI	12000	900	5.2"	50
13	T4	G24q-1	<b>S6730</b>	CF13DD/E/830	3000K 82CRI	12000	900	5.2"	50
13	T4	G24q-1	<b>S6731</b>	CF13DD/E/835	3500K 82CRI	12000	900	5.2"	50
13	T4	G24q-1	<b>S6732</b>	CF13DD/E/841	4100K 82CRI	12000	900	5.2"	50
18	T4	G24q-2	<b>S6733</b>	CF18DD/E/827	2700K 82CRI	12000	1250	5.8"	50
18	T4	G24q-2	<b>S6734</b>	CF18DD/E/830	3000K 82CRI	12000	1250	5.8"	50
18	T4	G24q-2	<b>S6735</b>	CF18DD/E/835	3500K 82CRI	12000	1250	5.8"	50
18	T4	G24q-2	<b>S6736</b>	CF18DD/E/841	4100K 82CRI	12000	1250	5.8"	50
26	T4	G24q-3	<b>S6737</b>	CF26DD/E/827	2700K 82CRI	12000	1825	6.5"	50
26	T4	G24q-3	<b>S6738</b>	CF26DD/E/830	3000K 82CRI	12000	1825	6.5"	50
26	T4	G24q-3	<b>S6739</b>	CF26DD/E/835	3500K 82CRI	12000	1825	6.5"	50
26	T4	G24q-3	<b>S6740</b>	CF26DD/E/841	4100K 82CRI	12000	1825	6.5"	50

fluorescent lamps

# Compact Fluorescent

## Four Pin Electronic

## Triple Tube

### Color Reference Guide

827 = 2700K Warm White  
 830 = 3000K Soft White  
 835 = 3500K Neutral  
 841 = 4100K Cool White



**CF13DT/E**

**13 Watt**

G24q-1 4 Pin Base

- S4369** CF13DT/E/827
- S4370** CF13DT/E/830
- S4371** CF13DT/E/835
- S4372** CF13DT/E/841

Packing:50/Master,  
Individually Boxed



**CF18DT/E**

**18 Watt**

GX24q-2 4 Pin Base

- S6741** CF18DT/E/IN/827
- S6742** CF18DT/E/IN/830
- S6743** CF18DT/E/IN/835
- S6744** CF18DT/E/IN/841

Packing:50/Master,  
Individually Boxed



**CF26DT/E**

**26 Watt**

GX24q-3 4 Pin Base

- S6745** CF26DT/E/IN/827
- S6746** CF26DT/E/IN/830
- S6747** CF26DT/E/IN/835
- S6748** CF26DT/E/IN/841

Packing:50/Master,  
Individually Boxed

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
13	T4	GX24Q-1	<b>S4369</b>	CF13DT/E/827	2700K 82CRI	12000	900	4.2"	50
13	T4	GX24Q-1	<b>S4370</b>	CF13DT/E/830	3000K 82CRI	12000	900	4.2"	50
13	T4	GX24Q-1	<b>S4371</b>	CF13DT/E/835	3500K 82CRI	12000	900	4.2"	50
13	T4	GX24Q-1	<b>S4372</b>	CF13DT/E/841	4100K 82CRI	12000	900	4.2"	50
18	T4	GX24q-2	<b>S6741</b>	CF18DT/E/IN/827	2700K 82CRI	12000	1200	4.4"	50
18	T4	GX24q-2	<b>S6742</b>	CF18DT/E/IN/830	3000K 82CRI	12000	1200	4.4"	50
18	T4	GX24q-2	<b>S6743</b>	CF18DT/E/IN/835	3500K 82CRI	12000	1200	4.4"	50
18	T4	GX24q-2	<b>S6744</b>	CF18DT/E/IN/841	4100K 82CRI	12000	1200	4.4"	50
26	T4	GX24q-3	<b>S6745</b>	CF26DT/E/IN/827	2700K 82CRI	12000	1800	5.0"	50
26	T4	GX24q-3	<b>S6746</b>	CF26DT/E/IN/830	3000K 82CRI	12000	1800	5.0"	50
26	T4	GX24q-3	<b>S6747</b>	CF26DT/E/IN/835	3500K 82CRI	12000	1800	5.0"	50
26	T4	GX24q-3	<b>S6748</b>	CF26DT/E/IN/841	4100K 82CRI	12000	1800	5.0"	50

# Compact Fluorescent

## *Four Pin Electronic*

### Triple Tube

Not Shown Actual Size



**CF57DT/E**

**57 Watt**

GX24q-5 4 Pin Base

- S6421** CF57DT/E/IN/827
- S6422** CF57DT/E/IN/830
- S6423** CF57DT/E/IN/835
- S6424** CF57DT/E/IN/841

Packing:  
50/Master,  
Individually Boxed



**CF42DT/E**

**42 Watt**

GX24q-4 4 Pin Base

- S6753** CF42DT/E/IN/827
- S6754** CF42DT/E/IN/830
- S6755** CF42DT/E/IN/835
- S6756** CF42DT/E/IN/841

Packing:  
50/Master,  
Individually Boxed



**CF32DT/E**

**32 Watt**

GX24q-3 4 Pin Base

- S6749** CF32DT/E/IN/827
- S6750** CF32DT/E/IN/830
- S6751** CF32DT/E/IN/835
- S6752** CF32DT/E/IN/841

Packing:  
50/Master,  
Individually Boxed

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Pack. Type	Mst. Ctn./ Inner Pack
32	T4	GX24q-3	<b>S6749</b>	CF32DT/E/IN/827	2700K 82CRI	12000	2400	5.6"	Box	50
32	T4	GX24q-3	<b>S6750</b>	CF32DT/E/IN/830	3000K 82CRI	12000	2400	5.6"	Box	50
32	T4	GX24q-3	<b>S6751</b>	CF32DT/E/IN/835	3500K 82CRI	12000	2400	5.6"	Box	50
32	T4	GX24q-3	<b>S6752</b>	CF32DT/E/IN/841	4100K 82CRI	12000	2400	5.6"	Box	50
42	T4	GX24q-4	<b>S6753</b>	CF42DT/E/IN/827	2700K 82CRI	12000	3200	6.5"	Box	50
42	T4	GX24q-4	<b>S6754</b>	CF42DT/E/IN/830	3000K 82CRI	12000	3200	6.5"	Box	50
42	T4	GX24q-4	<b>S6755</b>	CF42DT/E/IN/835	3500K 82CRI	12000	3200	6.5"	Box	50
42	T4	GX24q-4	<b>S6756</b>	CF42DT/E/IN/841	4100K 82CRI	12000	3200	6.5"	Box	50
57	T4	GX24q-5	<b>S6421</b>	CF57DT/E/IN/827	2700K 82CRI	12000	4300	7.76"	Box	50
57	T4	GX24q-5	<b>S6422</b>	CF57DT/E/IN/830	3000K 82CRI	12000	4300	7.76"	Box	50
57	T4	GX24q-5	<b>S6423</b>	CF57DT/E/IN/835	3500K 82CRI	12000	4300	7.76"	Box	50
57	T4	GX24q-5	<b>S6424</b>	CF57DT/E/IN/841	4100K 82CRI	12000	4300	7.76"	Box	50

fluorescent lamps

# Compact Fluorescent

## Long Twin Tube

2G11 Base

fluorescent lamps



### 18 Watt

**S6757** FT18DL/830  
**S2964** FT18DL/830/RS  
**S6758** FT18DL/835  
**S2965** FT18DL/835/RS  
**S6759** FT18DL/841  
**S2966** FT18DL/841/RS

### 40 Watt

**S6766** FT40DL/830/RS  
**S6767** FT40DL/835/RS  
**S6768** FT40DL/841/RS

### 24 Watt

**S6760** FT24DL/830  
**S6761** FT24DL/835  
**S6762** FT24DL/841

### 50 Watt

**S2967** PLL50W/830/RS  
**S2968** PLL50W/835/RS  
**S2969** PLL50W/841/RS

### 36 Watt

**S6763** FT36DL/830  
**S6764** FT36DL/835  
**S6765** FT36DL/841

### 55 Watt

**S6769** FT55DL/830  
**S6770** FT55DL/835  
**S6771** FT55DL/841

#### Color Reference Guide

830 = 3000K Soft White  
 835 = 3500K Neutral  
 841 = 4100K Cool White

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Description	Avg. Rated Hours	Initial Lumens	Nominal Length	Carton
18	T5	2G11	<b>S6757</b>	FT18DL/830	3000K 82CRI	12000	1250	9.0"	10
18	T5	2G11	<b>S2964</b>	FT18DL/830/RS	3000K 82CRI	20000	1250	10.5"	10
18	T5	2G11	<b>S6758</b>	FT18DL/835	3500K 82CRI	12000	1250	9.0"	10
18	T5	2G11	<b>S2965</b>	FT18DL/835/RS	3500K 82CRI	20000	1250	10.5"	10
18	T5	2G11	<b>S6759</b>	FT18DL/841	4100K 82CRI	12000	1250	9.0"	10
18	T5	2G11	<b>S2966</b>	FT18DL/841/RS	4100K 82CRI	20000	1250	10.5"	10
24	T5	2G11	<b>S6760</b>	FT24DL/830	3000K 82CRI	12000	1800	12.9"	10
24	T5	2G11	<b>S6761</b>	FT24DL/835	3500K 82CRI	12000	1800	12.9"	10
24	T5	2G11	<b>S6762</b>	FT24DL/841	4100K 82CRI	12000	1800	12.9"	10
36	T5	2G11	<b>S6763</b>	FT36DL/830	3000K 82CRI	12000	2900	16.6"	10
36	T5	2G11	<b>S6764</b>	FT36DL/835	3500K 82CRI	12000	2900	16.6"	10
36	T5	2G11	<b>S6765</b>	FT36DL/841	4100K 82CRI	12000	2900	16.6"	10
40	T5	2G11	<b>S6766</b>	FT40DL/830/RS	3000K 82CRI	20000	3150	22.6"	10
40	T5	2G11	<b>S6767</b>	FT40DL/835/RS	3500K 82CRI	20000	3150	22.6"	10
40	T5	2G11	<b>S6768</b>	FT40DL/841/RS	4100K 82CRI	20000	3150	22.6"	10
50	T5	2G11	<b>S2967</b>	PLL 50W/830/RS	3000K 82CRI	14000	4300	22.5"	25
50	T5	2G11	<b>S2968</b>	PLL 50W/835/RS	3500K 82CRI	14000	4300	22.5"	25
50	T5	2G11	<b>S2969</b>	PLL 50W/841/RS	4100K 82CRI	14000	4300	22.5"	25
55	T5	2G11	<b>S6769</b>	FT55DL/830	3000K 82CRI	12000	4800	21.1"	10
55	T5	2G11	<b>S6770</b>	FT55DL/835	3500K 82CRI	12000	4800	21.1"	10
55	T5	2G11	<b>S6771</b>	FT55DL/841	4100K 82CRI	12000	4800	21.1"	10

# Compact Fluorescent *Specialty* Tubes



## Dulux-T

18 Watt

**S4367** CF18DT/827

26 Watt

**S4368** CF26DT/827

Packing: 50/Master,  
Individually Sleeved

## Quad

22 Watt

**S6020** FDL22LE/D

**S6021** FDL22EX/D

28 Watt

**S6022** FDL28LE/D

**S6023** FDL28EX/D

Packing: 50/Master,  
Individually Sleeved

## Dulux-L

18 Watt

**S6772** CF18DF/830

**S6773** CF18DF/841

24 Watt

**S6774** CF24DF/830

**S6775** CF24DF/841

36 Watt

**S6776** CF36DF/830

**S6777** CF36DF/841

Packing: 10/Master,  
Individually Sleeved

### Color Reference Guide

830 = 3000K Soft White

835 = 3500K Neutral

841 = 4100K Cool White

### Not Shown Actual Size

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Description	Avg. Rated Hours	Lumens	Length	Pack. Type	Mst. Ctn./ Inner Pack
22	T5	GX32D-2	<b>S6020</b>	FDL22LE/D	2800K 84CRI	10000	1200	6.0"	Sleeve	50
22	T5	GX32D-2	<b>S6021</b>	FDL22EX/D	5000K 84CRI	10000	1200	6.0"	Sleeve	50
28	T5	GX32D-3	<b>S6022</b>	FDL28LE/D	2800K 84CRI	10000	1600	6.8"	Sleeve	50
28	T5	GX32D-3	<b>S6023</b>	FDL28EX/D	5000K 84CRI	10000	1600	6.8"	Sleeve	50
18	T4	GX24D-2	<b>S4367</b>	CF18DT/827	2700K 82CRI	12000	1200	4.8"	Box	50
26	T4	GX24D-3	<b>S4368</b>	CF26DT/827	2700K 82CRI	12000	1800	5.4"	Box	50
18	T5	2G10	<b>S6772</b>	CF18DF/830	3000K 82CRI	10000	1100	4.8"	Sleeve	10
18	T5	2G10	<b>S6773</b>	CF18DF/841	4100K 82CRI	10000	1100	4.8"	Sleeve	10
24	T5	2G10	<b>S6774</b>	CF24DF/830	3000K 82CRI	10000	1700	6.7"	Sleeve	10
24	T5	2G10	<b>S6775</b>	CF24DF/841	4100K 82CRI	10000	1700	6.7"	Sleeve	10
36	T5	2G10	<b>S6776</b>	CF36DF/830	3000K 82CRI	10000	2800	8.5"	Sleeve	10
36	T5	2G10	<b>S6777</b>	CF36DF/841	4100K 82CRI	10000	2800	8.5"	Sleeve	10

# Compact Fluorescent



## Mini Spirals

Not Shown Actual Size



**Mini Spiral**



**Mini Spiral  
(Candelabra Base)**

**MINI SPIRALS** Their petite size and high lumen output have made this series the CFL of choice. These minis are suitable for many applications such as, table lamps, wall sconces, chandeliers with shades and task lighting with reflectors.

- 2700K, 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified\*

Watts	Base	Satco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	Length	Mst. Ctn./ Inner Pack
5	E26/Med.	<b>S6298</b>	EFMSP5/27	2700K	10000	120	250	82	4.06"	6/24 Box
9	E26/Med.	<b>S6200*</b>	EFMSP9/30	3000K	10000	120	500	82	4.45"	6/24 Blister
11	E26/Med.	<b>S6201*</b>	EFMSP11/30	3000K	6000	120	550	82	4.76"	6/24 Blister
13	E26/Med.	<b>S6202*</b>	EFMSP13/30	3000K	10000	120	800	82	4.96"	6/24 Blister
15	E26/Med.	<b>S6203*</b>	EFMSP15/30	3000K	10000	120	900	82	4.80"	6/24 Blister
18	E26/Med.	<b>S6243*</b>	EFMSP18/30	3000K	10000	120	1100	82	5.28"	6/24 Blister
26	E26/Med.	<b>S6204</b>	EFMSP26/30	3000K	10000	120	1600	82	5.94"	6/24 Blister
13	E26/Med.	<b>S6223</b>	EFMSP13/50	5000K	10000	120	800	82	4.96"	6/24 Blister
15	E26/Med.	<b>S6224</b>	EFMSP15/50	5000K	10000	120	900	82	4.80"	6/24 Blister
26	E26/Med.	<b>S6225</b>	EFMSP26/50	5000K	10000	120	1600	82	5.94"	6/24 Blister
5	E12/Cand.	<b>S6297</b>	EFMSP5/27	2700K	10000	120	250	82	4.13"	6/24 Box
9	E12/Cand.	<b>S6251</b>	EFMSP9/30	3000K	10000	120	500	82	4.45"	6/24 Blister
11	E12/Cand.	<b>S6252</b>	EFMSP11/30	3000K	6000	120	550	82	4.76"	6/24 Blister
13	E12/Cand.	<b>S6253</b>	EFMSP13/30	3000K	10000	120	800	82	4.96"	6/24 Blister
<b>230V</b>										
13	E27/Med.	<b>S6247</b>	EFMSP13/50	5000K	10000	230	800	82	4.96"	6/24 Blister
26	E27/Med.	<b>S6248</b>	EFMSP26/50	5000K	10000	230	1600	82	5.94"	6/24 Blister

\*Energy Star Certified

fluorescent lamps



*3-Way Spiral*



*Dimmable Spiral*



*Standard Spiral*

- Dimmable & 3-Way Models
- 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified\*



**STANDARD SPIRALS** Our new line of full size spiral lamps now feature a 23 watt dimmable model and our new 12/20/26 watt 3-way CFL. Other choices include lamps available in wattages from 15 to 32 watts in two color temperatures.

Watts	Base	Satco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	Length	Mst.Ctn./ Inner Pack
15	E26/Med.	<b>S6205*</b>	EFSP15/30	3000K	6000	120	900	82	5.35"	6/24 Blister
20	E26/Med.	<b>S6206*</b>	EFSP20/30	3000K	6000	120	1200	82	5.67"	6/24 Blister
23	E26/Med.	<b>S6207*</b>	EFSP23/30	3000K	6000	120	1380	82	6.02"	6/24 Blister
26	E26/Med.	<b>S6209*</b>	EFSP26/30	3000K	6000	120	1600	82	6.14"	6/24 Blister
32	E26/Med.	<b>S6210*</b>	EFSP32/30	3000K	6000	120	1920	82	6.73"	6/24 Blister
15	E26/Med.	<b>S6226</b>	EFSP15/50	5000K	6000	120	900	82	5.35"	6/24 Blister
20	E26/Med.	<b>S6227</b>	EFSP20/50	5000K	6000	120	1200	82	5.67"	6/24 Blister
23	E26/Med.	<b>S6228</b>	EFSP23/50	5000K	6000	120	1380	82	6.02"	6/24 Blister
26	E26/Med.	<b>S6229</b>	EFSP26/50	5000K	6000	120	1600	82	6.14"	6/24 Blister
32	E26/Med.	<b>S6240</b>	EFSP32/50	5000K	6000	120	1920	82	6.73"	6/24 Blister
12/20/26	E26/Med.	<b>S6211*</b>	EFSP12-26/30/3WAY	3000K	6000	120	660/1200/1600	82	6.02"	6/24 Blister
23	E26/Med.	<b>S6212*</b>	EFSP23/30/DIM	3000K	6000	120	1380	82	6.02"	6/24 Blister

\*Energy Star Certified

# Compact Fluorescent R20 Reflectors



6000 Hours

Not Shown Actual Size



R20

Reflector



R20

Reflector  
(Long)

**R E F L E C T O R S**  
Compact, sleek and efficient describe this latest series of energy saving reflectors. Technology has enabled us to develop these 21st century products; their performance and appearance rival their incandescent counterparts.

- 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified\*



Watts	Base	Salco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	Length	Mst. Ctn./ Inner Pack
5	E26/Med.	S6244*	EFR205/30	3000K	6000	120	260	82	4.21"	6/24 Blister
11	E26/Med.	S6245	EFR20L11/30	3000K	6000	120	330	82	4.96"	6/24 Blister
<b>230V</b>										
11	E27/Med.	S6249	EFR20L11/50	5000K	6000	230	330	82	4.96"	6/24 Blister

fluorescent lamps





# Compact Fluorescent **R30 & BR38** Reflectors

6000 Hours



Not Shown Actual Size



<b>WET LOCATION</b>	<b>BR38</b>	<b>R30</b>	<b>R30</b>
	<b>Outdoor Reflector</b>	<b>Dimmable Reflector</b>	<b>Reflector</b>

**REFLECTORS** Our new 23 watt PAR38 reflector delivers a high lumen punch of light while being Energy Star certified and U.L. listed for wet location applications. Also new is our "Dimmable" R30 reflector.

- 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified\*



Watts	Base	Satco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	Length	Mst.Ctn./ Inner Pack
15	E26/Med.	<b>S6213*</b>	EFR3015/30	3000K	6000	120	550	82	5.39"	6/24 Blister
15	E26/Med.	<b>S6255*</b>	EFR3015/DIM/30	3000K	6000	120	525	82	6.10"	6/24 Blister
23	E26/Med.	<b>S6215*</b>	EFPAR3823/30	3000K	6000	120	960	82	6.50"	6/24 Blister

\*Energy Star Certified

fluorescent lamps

# Compact Fluorescent



## R40 Reflectors

6000 Hours

Not Shown Actual Size



R40

Reflector

R40

Dimmable  
Reflector

**R E F L E C T O R S**  
Compact, sleek and efficient describe this latest series of energy saving reflectors.

- 3000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified\*



Watts	Base	Satco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	Length	Mst.Ctn./ Inner Pack
23	E26/Med.	S6214*	EFR4023/30	3000K	6000	120	920	82	6.50"	6/24 Blister
23	E26/Med.	S6256	EFR4023/DIM/30	3000K	6000	120	920	82	7.00"	6/24 Blister

\*Energy Star Certified

fluorescent lamps



# Compact Fluorescent

6000 Hours

# A Type Household Bulbs



Not Shown Actual Size

<b>15W</b>	<b>11W</b>	<b>9W</b>	<b>7W</b>
Household Bulb	Household Bulb	Household Bulb	Household Bulb

**A-TYPE BULBS** This collection provides an aesthetic value to these functional products. The compact A-type lamp delivers impressive lumen performance for an enclosed lamp.

- 3000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified\*



Watts	Base	Satco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	Length	Mst.Ctn./ Inner Pack
7	E26/Med.	<b>S6233*</b>	EF7A19/30	3000K	6000	120	300	82	4.54"	6/24 Blister
9	E26/Med.	<b>S6239*</b>	EF9A19/30	3000K	6000	120	450	82	4.61"	6/24 Blister
11	E26/Med.	<b>S6246*</b>	EF11A19/30	3000K	6000	120	540	82	4.96"	6/24 Blister
15	E26/Med.	<b>S6216*</b>	EF15A19/30	3000K	6000	120	720	82	5.39"	6/24 Blister

\*Energy Star Certified

fluorescent lamps

# Compact Fluorescent Bulbs



fluorescent lamps



- 3000K & 5000K Color Temperatures
- 6000 Hours Lamp Life
- Energy Star Certified\*



Not Shown Actual Size

Watts	Base	Salco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	Length	Mst. Ctn./ Inner Pack
3	E12/Cand.	<b>S6219</b>	EFTOR3/30	3000K	6000	120	120	82	4.96"	6/24 Blister
7	E12/Cand.	<b>S6220</b>	EFTOR7/30	3000K	6000	120	280	82	4.96"	6/24 Blister
3	E26/Med.	<b>S6221</b>	EFTOR3/30	3000K	6000	120	120	82	4.96"	6/24 Blister
7	E26/Med.	<b>S6222*</b>	EFTOR7/30	3000K	6000	120	280	82	4.96"	6/24 Blister
15	E26/Med.	<b>S6217</b>	EFT15/30	3000K	6000	120	720	82	5.51"	6/24 Blister
15	E26/Med.	<b>S6241</b>	EFT15/50	5000K	6000	120	720	82	5.51"	6/24 Blister
15	E26/Med.	<b>S6218*</b>	EFG15/30	3000K	6000	120	720	82	5.39"	6/24 Blister
15	E26/Med.	<b>S6242</b>	EFG15/50	5000K	6000	120	720	82	5.39"	6/24 Blister
15	E27/Med.	<b>S6250</b>	EFG15/50/230	5000K	6000	230	720	82	5.39"	6/24 Blister

\*Energy Star Certified



**23W**  
**Spiral Bulb**

*with Dual Photocells*



**Mini Spiral**

*Bug Light*

Watts	Base	Satco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	Length	Mst.Ctn./ Inner Pack
15	E26/Med.	<b>S6254</b>	EFMSP15/BUG	N/A	10000	120	N/A	N/A	4.88"	6/24 Blister
23	E26/Med.	<b>S6257</b>	EF23/SPL/PHOTO/30	3000K	6000	120	1060	>75	2.5"	6/24 Blister

*Not Shown Actual Size*

# Fluorescent *Specialty* Lamps



fluorescent lamps



**22W**

*Circline Style*

- 3000K & 6500K Color Temperatures • 10000 Hours

*Not Shown Actual Size*

Watts	Base	Satco Order No.	Lamp Code	Color Temp.	Avg. Rated Hours	Volts	Lumens	CRI	M.O.L.	Mst.Ctn./ Inner Pack
22	E26/Med.	<b>S6259</b>	EF/FC8/T9/WW	3000K	10000	120	1060	52	3"	6/24 Blister
22	E26/Med.	<b>S6261</b>	EF/FC8/T9/D	6500K	10000	120	1060	76	3"	6/24 Blister

# Metal Halide

## Mogul Base



BT28

ED28

BT37

ED37

BT56

- Standard (Probe) Start
- Enclosed Rated
- Universal – Varied Burning Position



ED28

ED37

BT56

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	ANSI	Finish	Color Temp	CRI	Average Rated Hours	Initial Lumens	Operating Position	M.O.L.	Case
175	BT28	Mogul	<b>S4829</b>	MH175/U	M57/E	Clear	4000K	65	10000	14000	Univ.	8 5/16	6
175	ED28	Mogul	<b>S4830</b>	MH175/C/U	M57/E	Coated	3700K	70	10000	13300	Univ.	8 5/16	12
250	BT28	Mogul	<b>S4831</b>	MH250/U	M58/E	Clear	4000K	65	10000	21000	Univ.	8 5/16	6
250	ED28	Mogul	<b>S4832</b>	MH250/C/U	M58/E	Coated	3700K	70	10000	20000	Univ.	8 5/16	12
400	BT37	Mogul	<b>S4833</b>	MH400/U	M59/E	Clear	4000K	65	20000	36000	Univ.	11 1/2	6
400	ED37	Mogul	<b>S4834</b>	MH400/C/U	M59/E	Coated	3700K	70	20000	34000	Univ.	11 1/2	6
400	ED28	Mogul	<b>S4843</b>	MH400/U/ED28	M59/E	Clear	4000K	65	20000	36000	Univ.	8 5/16	12
400	ED28	Mogul	<b>S4844</b>	MH400/C/U/ED28	M59/E	Coated	3700K	70	20000	34000	Univ.	8 5/16	12
1000	BT56	Mogul	<b>S4835</b>	MH1000/U	M47/E	Clear	4000K	65	18000	110000	Univ.	15 3/8	6
1000	BT56	Mogul	<b>S4836</b>	MH1000/C/U	M47/E	Coated	3700K	70	12000	105000	Univ.	15 3/8	6
1000	BT37	Mogul	<b>S4845</b>	MH1000/U/BT37	M47/E	Clear	4000K	65	12000	110000	Univ.	11 1/2	6
1500	BT56	Mogul	<b>S4837</b>	MH1500/HBU	M48/E	Clear	3400K	65	3000	161000	BU 105	15 3/8	6
1500	BT56	Mogul	<b>S4839</b>	MH1500/U/XL	M48/E	Clear	4000K	65	6000	170000	Univ.	15 3/8	6

\*Hours and lumens are based on vertical burning position • When used horizontally, hours and lumens are reduced.

# Metal Halide

## Medium Base



**ED17**  
Clear

**ED17**  
Coated

For Use in Enclosed Rated Fixtures •

### PULSE START

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	ANSI	Finish	Color Temp.	CRI	Average Rated Hours	Initial Lumens	Operating Position	M.O.L.	Case
50	ED17	Med.	<b>S4854</b>	MH50/U/MED/PS	M110/E	Clear	4000K	65	10000	3400	Univ.	5 7/16	12
50	ED17	Med.	<b>S4855</b>	MH50/C/U/MED/PS	M110/E	Coated	3700K	70	10000	3200	Univ.	5 7/16	12
70	ED17	Med.	<b>S4856</b>	MH70/U/MED/PS	M98/E	Clear	4000K	65	10000	5600	Univ.	5 7/16	12
70	ED17	Med.	<b>S4857</b>	MH70/C/U/MED/PS	M98/E	Coated	3700K	70	10000	5300	Univ.	5 7/16	12
100	ED17	Med.	<b>S4858</b>	MH100/U/MED/PS	M90/E	Clear	4000K	65	10000	9000	Univ.	5 7/16	12
100	ED17	Med.	<b>S4859</b>	MH100/C/U/MED/PS	M90/E	Coated	3700K	70	10000	8500	Univ.	5 7/16	12
150	ED17	Med.	<b>S4860</b>	MH150/U/MED/PS	M102/E	Clear	4000K	65	10000	14000	Univ.	5 7/16	12
150	ED17	Med.	<b>S4861</b>	MH150/C/U/MED/PS	M102/E	Coated	3700K	70	10000	13300	Univ.	5 7/16	12

### STANDARD PROBE START

175	ED17	Med.	<b>S4862</b>	MH175/U/MED	M57/E	Clear	4000K	65	10000	14000	Univ.	5 7/16	12
175	ED17	Med.	<b>S4863</b>	MH175/C/U/MED	M57/E	Coated	3700K	70	10000	13300	Univ.	5 7/16	12



**EDX17**  
Clear

**EDX17**  
Coated

For Use in Open or Enclosed Rated Fixtures •

### PULSE START

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	ANSI	Finish	Color Temp.	CRI	Avg. Rated Hours	Initial Lumens	Operating Position	Case
50	EDX17	Med.	<b>S4846</b>	MP50/U/UVS/3K/PS	M110/O	Clear	3000K	65	10000	3200	Univ.	12
50	EDX17	Med.	<b>S4847</b>	MP50/C/U/UVS/3K/PS	M110/O	Coated	3200K	70	10000	3000	Univ.	12
70	EDX17	Med.	<b>S4848</b>	MP70/U/UVS/PS	M98/O	Clear	4000K	65	10000	5300	Univ.	12
70	EDX17	Med.	<b>S4849</b>	MP70/C/U/UVS/PS	M98/O	Coated	3700K	70	10000	5000	Univ.	12
100	EDX17	Med.	<b>S4850</b>	MP100/U/UVS/PS	M90/O	Clear	4000K	65	10000	8500	Univ.	12
100	EDX17	Med.	<b>S4851</b>	MP100/C/U/UVS/PS	M90/O	Coated	3700K	70	10000	8100	Univ.	12
150	EDX17	Med.	<b>S4852</b>	MP150/U/UVS/PS	M102/O	Clear	4000K	65	10000	13300	Univ.	12
150	EDX17	Med.	<b>S4853</b>	MP150/C/U/UVS/PS	M102/O	Coated	3700K	70	10000	12600	Univ.	12

### STANDARD PROBE START

175	EDX17	Med.	<b>S4828</b>	MP175/BU-ONLY/MED	M57/O	Clear	3600K	65	10000	14400	Base Up	20
-----	-------	------	--------------	-------------------	-------	-------	-------	----	-------	-------	---------	----

\*Hours and lumens are based on vertical burning position • When used horizontally, hours and lumens are reduced.



# Metal Halide

## Medium Base



**ED17**  
Clear

**ED17**  
Coated

For Use in Enclosed Rated Fixtures •

### PULSE START

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	ANSI	Finish	Color Temp.	CRI	Average Rated Hours	Initial Lumens	Operating Position	M.O.L.	Case
50	ED17	Med.	<b>S4854</b>	MH50/U/MED/PS	M110/E	Clear	4000K	65	10000	3400	Univ.	5 7/16	12
50	ED17	Med.	<b>S4855</b>	MH50/C/U/MED/PS	M110/E	Coated	3700K	70	10000	3200	Univ.	5 7/16	12
70	ED17	Med.	<b>S4856</b>	MH70/U/MED/PS	M98/E	Clear	4000K	65	10000	5600	Univ.	5 7/16	12
70	ED17	Med.	<b>S4857</b>	MH70/C/U/MED/PS	M98/E	Coated	3700K	70	10000	5300	Univ.	5 7/16	12
100	ED17	Med.	<b>S4858</b>	MH100/U/MED/PS	M90/E	Clear	4000K	65	10000	9000	Univ.	5 7/16	12
100	ED17	Med.	<b>S4859</b>	MH100/C/U/MED/PS	M90/E	Coated	3700K	70	10000	8500	Univ.	5 7/16	12
150	ED17	Med.	<b>S4860</b>	MH150/U/MED/PS	M102/E	Clear	4000K	65	10000	14000	Univ.	5 7/16	12
150	ED17	Med.	<b>S4861</b>	MH150/C/U/MED/PS	M102/E	Coated	3700K	70	10000	13300	Univ.	5 7/16	12

### STANDARD PROBE START

175	ED17	Med.	<b>S4862</b>	MH175/U/MED	M57/E	Clear	4000K	65	10000	14000	Univ.	5 7/16	12
175	ED17	Med.	<b>S4863</b>	MH175/C/U/MED	M57/E	Coated	3700K	70	10000	13300	Univ.	5 7/16	12



**EDX17**  
Clear

**EDX17**  
Coated

For Use in Open or Enclosed Rated Fixtures •

### PULSE START

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	ANSI	Finish	Color Temp.	CRI	Avg. Rated Hours	Initial Lumens	Operating Position	Case
50	EDX17	Med.	<b>S4846</b>	MP50/U/UVS/3K/PS	M110/O	Clear	3000K	65	10000	3200	Univ.	12
50	EDX17	Med.	<b>S4847</b>	MP50/C/U/UVS/3K/PS	M110/O	Coated	3200K	70	10000	3000	Univ.	12
70	EDX17	Med.	<b>S4848</b>	MP70/U/UVS/PS	M98/O	Clear	4000K	65	10000	5300	Univ.	12
70	EDX17	Med.	<b>S4849</b>	MP70/C/U/UVS/PS	M98/O	Coated	3700K	70	10000	5000	Univ.	12
100	EDX17	Med.	<b>S4850</b>	MP100/U/UVS/PS	M90/O	Clear	4000K	65	10000	8500	Univ.	12
100	EDX17	Med.	<b>S4851</b>	MP100/C/U/UVS/PS	M90/O	Coated	3700K	70	10000	8100	Univ.	12
150	EDX17	Med.	<b>S4852</b>	MP150/U/UVS/PS	M102/O	Clear	4000K	65	10000	13300	Univ.	12
150	EDX17	Med.	<b>S4853</b>	MP150/C/U/UVS/PS	M102/O	Coated	3700K	70	10000	12600	Univ.	12

### STANDARD PROBE START

175	EDX17	Med.	<b>S4828</b>	MP175/BU-ONLY/MED	M57/O	Clear	3600K	65	10000	14400	Base Up	20
-----	-------	------	--------------	-------------------	-------	-------	-------	----	-------	-------	---------	----

\*Hours and lumens are based on vertical burning position • When used horizontally, hours and lumens are reduced.

# Metal Halide

- Mogul Base
- Standard (Probe) Start
- Enclosed Rated
- Specified Burning Position



Watts	Bulb Type	Base*	Salco Order No.	Lamp Code	ANSI	Finish	Color Temp.	CRI	Avg. Rated Hours	Initial Lumens	Operating Position	MOL	Case
175	ED28	E39	<b>S4271</b>	MS175/BU	M57/E	Clear	4000K	65	10000	15000	BU±15°	8 5/16	12
175	ED28	EP39	<b>S4272</b>	MS175/HOR	M57/E	Clear	4000K	65	10000	15000	HOR± 45°	8 5/16	12
175	T15	E39	<b>S4840</b>	MH175/U/T15	M57/E	Clear	4000K	65	10000	14000	Univ.	8 5/16	12
250	ED28	E39	<b>S4273</b>	MS250/BU	M58/E	Clear	4000K	65	10000	23000	BU±15°	8 5/16	12
250	ED28	E39	<b>S4274</b>	MS250/C/BU	M58/E	Coated	3700K	70	10000	22000	BU±15°	8 5/16	12
250	ED28	EP39	<b>S4275</b>	MS250/HOR	M58/E	Clear	4000K	65	10000	23000	HOR± 45°	8 5/16	12
250	T15	E39	<b>S4841</b>	MH250/U/T15	M58/E	Clear	4000K	65	10000	21000	Univ.	8 5/16	12
250	T15	EP39	<b>S4868</b>	MS250/HOR/T15/3K	M58/E	Clear	3200K	65	10000	21000	HOR± 45°	8 5/16	12
400	ED37	E39	<b>S4276</b>	MS400/BU	M59/E	Clear	4000K	65	20000	40000	BU±15°	11 1/2	6
400	ED37	E39	<b>S4277</b>	MS400/C/BU	M59/E	Coated	3700K	70	20000	38000	BU±15°	11 1/2	6
400	ED28	E39	<b>S4278</b>	MS400/BU/ED28	M59/E	Clear	4000K	65	20000	40000	BU±15°	8 5/16	12
400	ED37	EP39	<b>S4279</b>	MS400/HOR	M59/E	Clear	4000K	65	20000	40000	HOR± 45°	11 1/2	6
400	ED37	EP39	<b>S4280</b>	MS400/C/HOR	M59/E	Coated	3700K	70	20000	38000	HOR± 45°	11 1/2	6
400	ED28	EP39	<b>S4281</b>	MS400/HOR/ED28	M59/E	Clear	4000K	65	20000	40000	HOR± 45°	8 5/16	12
400	T15	EP39	<b>S4842</b>	MH400/HBU/T15	M59/E	Clear	4000K	65	15000	36000	BU 90	9 3/4	12
400	T15	EP39	<b>S4282</b>	MS400/HOR/T15/3K	M59/E	Clear	3200K	65	15000	38000	HOR± 45°	9 3/4	12
1000	BT56	E39	<b>S4283</b>	MS1000/BU	M47/E	Clear	4000K	65	12000	115000	BU± 15°	15 3/8	6

\*Base Information

E39 = Standard Mogul Base

EP39 = Position Oriented Mogul Base

# Pulse Start Metal Halide



- Enclosed Rated •
- Specified •
- Burning Position

**ED37**  
Coated / Clear

**ED28**  
Coated / Clear

**ED17**  
Coated / Clear

Watts	Bulb Type	Base*	Salco Order No.	Lamp Code	ANSI	Finish	Color Temp.	CRI	Avg. Rated Hours	Initial Lumens	Operating Position	MOL	Case
175	ED17	Med	<b>S4234</b>	MS175/BU/MED/PS	M152/E	Clear	4000K	65	15000	17500	BU±15°	5 7/16	12
175	ED17	Med	<b>S4235</b>	MS175/C/BU/MED/PS	M152/E	Coated	3700K	70	15000	16600	BU±15°	5 7/16	12
175	ED28	Mog	<b>S4236</b>	MS175/BU/PS	M152/E	Clear	4000K	65	15000	17500	BU±15°	8 5/16	12
175	ED28	Mog	<b>S4237</b>	MS175/C/BU/PS	M152/E	Coated	3700K	70	15000	16600	BU±15°	8 5/16	12
200	ED17	Med	<b>S4238</b>	MS200/BU/MED/PS	M136/E	Clear	4000K	65	12000	21000	BU±15°	5 7/16	12
200	ED28	Mog	<b>S4291</b>	MS200V/PS	M136/E	Clear	4000K	65	15000	21000	Vert±15°	8 5/16	12
250	ED28	Mog	<b>S4239</b>	MS250V/PS	M153/E	Clear	4000K	65	15000	25000	Vert±15°	8 5/16	12
250	ED28	Mog	<b>S4240</b>	MS250/H75/PS	M153/E	Clear	4000K	65	15000	22000	Hor±5°	8 5/16	12
320	ED28	Mog	<b>S4241</b>	MS320V/ED28/PS	M154/E	Clear	4000K	65	20000	33000	Vert±15°	8 5/16	12
320	ED28	Mog	<b>S4242</b>	MS320/CV/ED28/PS	M154/E	Coated	3700K	70	20000	31000	Vert±15°	8 5/16	12
350	ED37	Mog	<b>S4243</b>	MS350V/PS	M131/E	Clear	4000K	65	20000	37000	Vert±15°	11 1/2	6
350	ED37	Mog	<b>S4244</b>	MS350/CV/PS	M131/E	Coated	3700K	70	20000	35000	Vert±15°	11 1/2	6
400	ED37	Mog	<b>S4245</b>	MS400V/PS	M155/E	Clear	4000K	65	20000	44000	Vert±15°	11 1/2	6
400	ED37	Mog	<b>S4246</b>	MS400/CV/PS	M155/E	Coated	3700K	70	20000	42000	Vert±15°	11 1/2	6
400	ED28	Mog	<b>S4247</b>	MS400V/ED28/PS	M155/E	Clear	4000K	65	20000	44000	Vert±15°	8 5/16	12
400	ED28	Mog	<b>S4248</b>	MS400/CV/ED28/PS	M155/E	Coated	3700K	70	20000	42000	Vert±15°	8 5/16	12
400	ED37	Mog	<b>S4249</b>	MS400/H75/PS	M155/E	Clear	4000K	65	20000	40000	Hor±75°	11 1/2	6
400	ED28	Mog	<b>S4250</b>	MS400/H75/ED28/PS	M155/E	Clear	4000K	65	20000	40000	Hor±75°	8 5/16	12



**ED37**  
Clear / Coated

**ED28**  
Clear / Coated

- Open Rated •
- UV Shield •
- Specified Burning Position •
- Mogul Base •

Watts	Bulb Type	Base*	Salco Order No.	Lamp Code	ANSI	Finish	Color Temp.	CRI	Avg. Rated Hours	Initial Lumens	Operating Position	MOL	Case
200	ED28	Mog EX39	<b>S4251</b>	MP200V/UVS/PS	M136/O	Clear	4000K	65	15000	20000	Vert±15°	8 5/16	12
250	ED28	Mog EX39	<b>S4252</b>	MP250/BU/UVS/PS	M153/O	Clear	4000K	65	15000	23800	BU±15°	8 5/16	12
320	ED28	Mog EX39	<b>S4253</b>	MP320/BU/ED28/UVS/PS	M154/O	Clear	4000K	65	20000	31000	BU±15°	8 5/16	12
320	ED28	Mog EX39	<b>S4254</b>	MP320/C/BU/ED28/UVS/PS	M154/O	Coated	3700K	70	20000	29000	BU±15°	8 5/16	12
320	ED37	Mog EX39	<b>S4255</b>	MP320/BU/ED37/UVS/PS	M154/O	Clear	4000K	65	20000	31000	BU±15°	11 1/2	6
350	ED37	Mog EX39	<b>S4256</b>	MP350V/UVS/PS	M131/O	Clear	4000K	65	20000	35000	Vert±15°	11 1/2	6
350	ED37	Mog EX39	<b>S4257</b>	MP350/CV/UVS/PS	M131/O	Coated	3700K	70	20000	33000	Vert±15°	11 1/2	6
400	ED37	Mog EX39	<b>S4258</b>	MP400/BU/UVS/PS	M155/O	Clear	4000K	65	20000	42000	BU±15°	11 1/2	6
400	ED37	Mog EX39	<b>S4259</b>	MP400/C/BU/UVS/PS	M155/O	Coated	3700K	70	20000	40000	BU±15°	11 1/2	6

# Metal Halide

- Ceramic Technology
- Par Type
- Open Rated
- Universal – Burning Position
- Medium Base



PAR20

PAR30

PAR38

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	ANSI	Beam	Initial Lumens	CBCP	Color Temp	CRI	Avg. Life Hours	M.O.L.	Position	Case
39	PAR20	Medium	S4284	CDM35PAR20/M/SP	M130/O	Spot 10°	2000	23000	3000K	81	9000	3 3/4	Universal	12
39	PAR20	Medium	S4285	CDM35PAR20/M/FL	M130/O	Flood 30°	2000	5000	3000K	81	9000	3 3/4	Universal	12
39	PAR30L	Medium	S4876	CDM35PAR30L/M/SP	M130/O	Spot 10°	2000	44000	3000K	81	9000	4 3/4	Universa	6
39	PAR30L	Medium	S4877	CDM35PAR30L/M/FL	M130/O	Flood 30°	2000	7400	3000K	81	9000	4 3/4	Universal	6
70	PAR30L	Medium	S4878	CDM70PAR30L/M/SP	M143/M98/O	Spot 10°	4800	68000	3000K	83	9000	4 3/4	Universal	6
70	PAR30L	Medium	S4879	CDM70PAR30L/M/FL	M143/M98/O	Flood 30°	4800	10000	3000K	83	9000	4 3/4	Universal	6
70	PAR38	Medium	S4897	CDM70PAR38/SP/3K	M143/M98/O	Spot 10°	4800	50000	3000K	82	10000	5 7/6	Universal	12
70	PAR38	Medium	S4812	CDM70PAR38/SP/4K	M143/M98/O	Spot 10°	4200	42000	4000K	92	10000	5 7/6	Universal	12
70	PAR38	Medium	S4898	CDM70PAR38/FL/3K	M143/M98/O	Flood 30°	4800	18000	3000K	82	10000	5 7/6	Universal	12
70	PAR38	Medium	S4813	CDM70PAR38/FL/4K	M143/M98/O	Flood 30°	4200	16000	4000K	92	10000	5 7/6	Universal	12
100	PAR38	Medium	S4888	CDM100PAR38/SP/3K	M140/M90/O	Spot 10°	6800	70000	3000K	85	12500	5 7/6	Universal	12
100	PAR38	Medium	S4814	CDM100PAR38/SP/4K	M140/M90/O	Spot 10°	6000	54000	4000K	93	10000	5 7/6	Universal	12
100	PAR38	Medium	S4889	CDM100PAR38/FL/3K	M140/M90/O	Flood 30°	6800	25000	3000K	85	12500	5 7/6	Universal	12
100	PAR38	Medium	S4869	CDM100PAR38/FL/4K	M140/M90/O	Flood 30°	6000	20000	4000K	93	10000	5 7/6	Universal	12

- R40 Reflector Type
- Enclosed rated
- Universal – Varied Burning Position
- Medium Base



R40

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	ANSI	Beam	Initial Lumens	CBCP	CCT(K)	C.R.I.	Avg. Life	M.O.L.	Operating Position	Case
175	R40	Medium	S4260	MH175W/U/R40/15	M57/E	Spot 10°	n/a	65000	4000K	65	10000	6 1/2	Universal	6
175	R40	Medium	S4261	MH175W/U/R40/70	M57/E	Flood 70°	n/a	6500	4000K	65	10000	6 1/2	Universal	6

# Metal Halide



70W/MH-DE



150W/MH-DE

- Double Ended Type
- Enclosed Rated

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	ANSI	Avg. Rated Life	Initial Lumens	CCT(K)	CRI	M.O.L.	Operating Position	Case
70	DE Tubular	RSC	<b>S4865</b>	MH-DE70/UVS/3K	Clear	M85/M98/E	10000	5200	3000	70	4 7/16	HOR±45°	25
70	DE Tubular	RSC	<b>S4864</b>	MH-DE70/UVS/4K	Clear	M85/M98/E	10000	5500	4200	65	4 7/16	HOR±45°	25
150	DE Tubular	RSC	<b>S4866</b>	MH-DE150/UVS/3K	Clear	M81/M102/E	10000	12500	3000	70	5 7/16	HOR±45°	25
150	DE Tubular	RSC	<b>S4867</b>	MH-DE150/UVS/4K	Clear	M81/M102/E	10000	12000	4200	65	5 7/16	HOR±45°	25
250	DE Tubular	Fc2	<b>S4262</b>	MH-DE250W/3K/Fc2	Clear	M80E	10000	20000	3000	70	6 1/2	HOR±45°	25
250	DE Tubular	Fc2	<b>S4263</b>	MH-DE250W/4K/Fc2	Clear	M80E	10000	20000	4200	70	6 1/2	HOR±45°	25



TD-6 - RX7



TD-7 - RX7



T-6  
G12

T-4  
G8.5

- Ceramic Technology
- Single Ended T Type
- Double Ended T Type
- Enclosed Rated
- Universal - Varied
- Burning Position

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	ANSI	Avg. Rated Life	Initial Lumens	Color Temp	CRI	M.O.L.	Operating Position	Case
39	SE Tubular	G8.5	<b>S4286</b>	CDM35/TC/830	Clear	M130/E	9000	3300	3000K	81	3 11/16	Universal	12
39	SE Tubular	G12	<b>S4288</b>	CDM35/T6/830	Clear	M130/E	12000	3400	3000K	81	3 5/16	Universal	12
70	SE Tubular	G8.5	<b>S4287</b>	CDM70/TC/830	Clear	M139/E	6000	6400	3000K	83	3 11/16	Universal	12
70	SE Tubular	G12	<b>S4289</b>	CDM70/T6/830	Clear	M139/E	12000	6600	3000K	81	3 5/16	Universal	12
70	SE Tubular	G12	<b>S4264</b>	CDM70/T6/942	Clear	M139/E	12000	6600	4200K	92	3 5/16	Universal	12
70	DE Tubular	RX7	<b>S4292</b>	CDM70/TD/830	Clear	M139/M85/E	15000	6500	3000K	82	4 11/16	HOR±45°	12
70	DE Tubular	RX7	<b>S4265</b>	CDM70/TD/942	Clear	M139/M85/E	15000	6000	4200K	92	4 11/16	HOR±45°	12
150	SE Tubular	G12	<b>S4290</b>	CDM150/T6/830	Clear	M142/E	12000	14000	3000K	85	4 11/16	Universal	12
150	SE Tubular	G12	<b>S4266</b>	CDM150/T6/942	Clear	M142/E	9000	12700	4200K	96	4 11/16	Universal	12
150	DE Tubular	RX7	<b>S4293</b>	CDM150/TD/830	Clear	M142/M102/M81/E	15000	13250	3000K	88	5 7/16	HOR±45°	12
150	DE Tubular	RX7	<b>S4267</b>	CDM150/TD/942	Clear	M142/M102/M81/E	15000	14200	4200K	96	5 7/16	HOR±45°	12

# Metal Halide

- Pulse Start
- Enclosed Rated
- Universal – Varied Burning Position

Not Shown Actual Size



Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	ANSI	Avg. Life Hours	Initial Lumens	Color Temp	CRI	M.O.L.	Operating Position	Case Qty.
70	ED28	Mog.	<b>S4230</b>	MH70/U/ED28/PS	Clear	M98/E	15000	5600	4000	65	8 5/8"	Univ.	12
100	ED28	Mog.	<b>S4231</b>	MH100/U/ED28/PS	Clear	M90/E	15000	9000	4000	65	8 5/8"	Univ.	12
125	ED17	Med.	<b>S4232</b>	MH125/HBU/PS	Clear	M150/E	15000	1200	4000	65	5 5/8"	BU±90°	12
150	ED28	Mog.	<b>S4233</b>	MH150/U/ED28/PS	Clear	M102/E	15000	14000	4000	65	8 5/8"	Univ.	12

- Energy Saver
- Standard Start
- Enclosed Rated
- Specified Burning Position
- Medium Base



Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	ANSI	Avg. Life Hours	Initial Lumens	Color Temp	CRI	M.O.L.	Operating Position	Case Qty.
360	ED37	E39/Mog.	<b>S4476</b>	MS360W/BU/EM	Clear	M165E	20000	36000	4000	65	11 1/2"	BU±15°	6
360	ED37	E39/Mog.	<b>S4477</b>	MS360W/C/BU/EM	Coated	M165E	20000	34200	3700	70	11 1/2"	BU±15°	6

# Metal Halide



Clear **ED37** Coated

- Open Rated
- Energy Saver
- Standard Start
- Specified Burning Position
- Mogul Base

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	ANSI	Avg. Life Hours	Initial Lumens	Color Temp	CRI	M.O.L.	Operating Position	Case
360	ED37	EX39/Mog.	<b>S4478</b>	MPI360W/BU/EM	Clear	M165O	20000	35000	4000	65	11½	BU±15°	6
360	ED37	EX39/Mog.	<b>S4479</b>	MPI360W/C/BU/EM	Coated	M165O	20000	34000	3700	70	11½	BU±15°	6



Clear **ED37** Coated **ED28**

- "White Lux" HPS Replacement
- Standard Start
- Enclosed Rated
- Specified Burning Position
- Mogul Base

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Finish	ANSI	Avg. Rated Hours	Initial Lumens	Color Temp	CRI	M.O.L.	Operating Position	Case
250	ED28	Mog.	<b>S4268</b>	MS250W/BU/LU	Clear	S50/E	10000	18500	4000	65	8 5/16	BU±15°	12
400	ED37	Mog.	<b>S4269</b>	MS400W/BU/LU	Clear	S51/E	20000	38000	4000	65	11½	BU±15°	6
400	ED37	Mog.	<b>S4270</b>	MS400W/C/BU/LU	Coated	S51/E	20000	36000	3700	70	11½	BU±15°	6

# Mercury Vapor

## Coated Finish

### Mogul Base

Not Shown Actual Size



**ED23 1/2**

**S1935** 100W H38JA-100/DX  
Packing: 12/Master



**ED28**

**S1934** 175W H39KC-175/DX  
**S1937** 250W H37KC-250/DX  
Packing: 12/Master



**ED37**

**S1938** 400W H33GL-400/DX  
Packing: 6/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Hours	Initial Lumens	M.O.L.	Case
100	ED23 1/2	Mogul	<b>S1935</b>	H38JA-100DX	Coated	10000	4000	7 1/2"	12
175	ED28	Mogul	<b>S1934</b>	H39KC-175DX	Coated	10000	7800	8 5/16"	12
250	ED28	Mogul	<b>S1937</b>	H37KC-250DX	Coated	10000	11200	8 5/16"	12
400	ED37	Mogul	<b>S1938</b>	H33GL-400DX	Coated	10000	22600	11 1/2"	12



# Mercury Vapor Clear & Coated



Not Shown Actual Size



**ED28**

**Clear  
Mogul Base**

**S1936** 175W H39KB-175  
Packing: 12/Master



**ED17**

**Coated  
Medium Base**

**S4474** 50W H45/46DL-40/50DX  
**S4475** 75W H43AV-75/DX  
Packing: 12/Master



**A23**

**Coated  
Medium Base**

**S1933** 100W H38MP-100/DX  
Packing: 12/Master

HID lamps

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Hours	Initial Lumens	M.O.L.	Case
50	ED17	Medium	<b>S4474</b>	H45/46DL-40/50DX	Coated	6000	1580	5 1/6"	12
75	ED17	Medium	<b>S4475</b>	H43AV-75/DX	Coated	6000	2700	5 1/6"	12
100	A23	Medium	<b>S1933</b>	H38MP-100DX	Coated	6000	4000	5 1/6"	12
175	ED28	Mogul	<b>S1936</b>	H39KB-175	Clear	10000	7800	8 1/6"	12

# High Pressure Sodium



## *Clear & Coated* Medium Base

Not Shown Actual Size



**E17**



**E17**

Four color retail display carton

- S5120** 35W LU35/D/MED
- S5121** 50W LU50/D/MED
- S3123** 70W LU70/D/MED
- S5125** 100W LU100/D/MED
- S5127** 150W LU150/55/D/MED

Packing: 20/Master

- S3130** 35W LU35/MED
- S3131** 50W LU50/MED
- S3127** 70W LU70/MED
- S3128** 100W LU100/MED
- S3129** 150W LU150/55/MED

Packing: 12/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Hours	Initial Lumens	M.O.L.	Case
35	E17	Medium	<b>S3130</b>	LU35/MED	Clear	16000	2250	5 7/16"	12
35	E17	Medium	<b>S5120</b>	LU35/D/MED	Coated	16000	2100	5 7/16"	20
50	E17	Medium	<b>S3131</b>	LU50/MED	Clear	24000	4000	5 7/16"	12
50	E17	Medium	<b>S5121</b>	LU50/D/MED	Coated	24000	3700	5 7/16"	20
70	E17	Medium	<b>S3127</b>	LU70/MED	Clear	24000	6300	5 7/16"	12
70	E17	Medium	<b>S5123</b>	LU70/D/MED	Coated	24000	5800	5 7/16"	20
100	E17	Medium	<b>S3128</b>	LU100/MED	Clear	24000	9500	5 7/16"	12
100	E17	Medium	<b>S5125</b>	LU100/D/MED	Coated	24000	8800	5 7/16"	20
150	E17	Medium	<b>S3129</b>	LU150/55/MED	Clear	24000	15800	5 11/16"	12
150	E17	Medium	<b>S5127</b>	LU150/55/D/MED	Coated	24000	14500	5 11/16"	20



# High Pressure Sodium

24,000 Hours

***Clear & Coated***

Not Shown Actual Size

Mogul Base



**ET23 1/2**



**ET23 1/2**

- S1929** 50W LU50
  - S1930** 70W LU70
  - S1931** 100W LU100
  - S1932** 150W LU150/55
- Packing: 12/Master

- S5122** 50W LU50/D
  - S5160** 70W LU70/D
  - S5126** 100W LU100/D
  - S5128** 150W LU150/55/D
- Packing: 20/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Hours	Initial Lumens	M.O.L.	Mst. Ctn./ Inner Pack
50	ET23 1/2	Mogul	<b>S1929</b>	LU50	Clear	24000	4000	7 3/4"	12
50	ET23 1/2	Mogul	<b>S5122</b>	LU50/D	Coated	24000	3700	7 3/4"	20
70	ET23 1/2	Mogul	<b>S1930</b>	LU70	Clear	24000	6300	7 3/4"	12
70	ET23 1/2	Mogul	<b>S5160</b>	LU70/D	Coated	24000	5500	7 3/4"	20
100	ET23 1/2	Mogul	<b>S1931</b>	LU100	Clear	24000	9500	7 3/4"	12
100	ET23 1/2	Mogul	<b>S5126</b>	LU100/D	Coated	24000	8800	7 3/4"	20
150	ET23 1/2	Mogul	<b>S1932</b>	LU150/55	Clear	24000	16000	7 3/4"	12
150	ET23 1/2	Mogul	<b>S5128</b>	LU150/55/D	Coated	24000	14000	7 3/4"	20

H I D L a m p s

# High Pressure Sodium



## Clear Mogul Base

24,000 Hours

Not Shown Actual Size



ET18

S5129 200W LU200/ECO  
 S1940 250W LU250  
 S5131 310W LU310/ECO  
 S1941 400W LU400



E25

S5124 1000W LU1000

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Hours	Initial Lumens	M.O.L.	Case
200	ET18	Mogul	S5129	LU200/ECO	Clear	24000	22000	9 5/8"	20
250	ET18	Mogul	S1940	LU250	Clear	24000	28000	9 5/8"	12
310	ET18	Mogul	S5131	LU310/ECO	Clear	24000	37000	9 5/8"	20
400	ET18	Mogul	S1941	LU400	Clear	24000	51000	9 5/8"	12
1000	E25	Mogul	S5124	LU1000	Clear	24000	130000	15 1/16"	6

# High Pressure Sodium

## *Clear & Coated* Mogul Base

24,000 Hours



**BT37**

**BT37**

**BT28**

**S5133** 750W LU750  
Packing: 6/Master

**S5132** 400W LU400/D  
Packing: 10/Master

**S5130** 250W LU250/D  
Packing: 10/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Hours	Initial Lumens	M.O.L.	Case
250	BT28	Mogul	<b>S5130</b>	LU250/D	Coated	24000	26000	8 31/32"	10
400	BT37	Mogul	<b>S5132</b>	LU400/D	Coated	24000	47500	11 1/2"	10
750	BT37	Mogul	<b>S5133</b>	LU750/ECO	Clear	24000	105000	11 1/2"	6

# Low Pressure

# Sodium Sox Lamps

16,000 Hours

## T17

**S4870** 18W SOX18W

**S4871** 35W SOX35W

**S4872** 55W SOX55W

Packing: 12/Master

## T21

**S4873** 90W SOX90W

**S4874** 135W SOX135W

Packing: 12/Master

**S4875** 180W SOX180W

Packing: 9/Master

Not Shown  
Actual Size



Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Avg. Rated Hours	Initial Lumens	Burning Position	M.O.L.	Case
18	T17	BY22d	<b>S4870</b>	SOX18W	Clear	16000	1800	BU±110°	8 ½"	12
35	T17	BY22d	<b>S4871</b>	SOX35W	Clear	16000	4500	BU±110°	12 ¾"	12
55	T17	BY22d	<b>S4872</b>	SOX55W	Clear	16000	7300	BU±110°	16 ¾"	12
90	T21	BY22d	<b>S4873</b>	SOX90W	Clear	16000	13500	H±20°	20 ¾"	12
135	T21	BY22d	<b>S4874</b>	SOX135W	Clear	16000	22000	H±20°	30 ½"	12
180	T21	BY22d	<b>S4875</b>	SOX180W	Clear	16000	30000	H±20°	44 ½"	9

# Sealed Beam Lamps

## PAR36

sealed beam lamps



PAR36 Screw Terminal

2 Piece Construction

Not Shown Actual Size

Watts	Bulb Type	Base	Salco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP	Filament	M.O.L.	Mst. Ctn./ Pack	Inner Type	Pack
<b>HALOGEN</b>													
36	PAR36	Screw Term.	S4807	36PAR36/CAP/VNSP	Spot 5°	12V	4000	17000	CC-8	2 3/4"	Box	12	
36	PAR36	Screw Term.	S4808	36PAR36/CAP/NSP	Spot 13°	12V	4000	3500	CC-8	2 3/4"	Box	12	
36	PAR36	Screw Term.	S4809	36PAR36/CAP/FL	Flood 32°	12V	4000	1000	CC-8	2 3/4"	Box	12	
50	PAR36	Screw Term.	S4806	50PAR36/CAP/NSP	Spot 6°	12V	4000	25000	CC-8	2 3/4"	Box	12	
<b>INCANDESCENT</b>													
50	PAR36	Screw Term.	S4804	50PAR36/WFL	Flood 30°	12V	2000	11500	CC-6	2 3/4"	Box	12	
50	PAR36	Screw Term.	S4805	50PAR36/SP	Spot 15°	12V	2000	11500	CC-6	2 3/4"	Box	12	
300	PAR56	Screw Term.	S4810	300PAR56/MFL	Flood 22°	120V	2000	24000	CC-13	5"	Box	8	
300	PAR56	Screw Term.	S4811	300PAR56/WFL	Flood 37°	120V	2000	11000	CC-13	5"	Box	8	
18	PAR36	Screw Term.	S4300	4014/Emergency Bldg. Lighting		6.4V	200			2 3/4"	Box	12	
12	PAR36	Screw Term.	S4301	4042/Emergency Bldg. Lighting		6.4V	150			2 3/4"	Box	12	
12	PAR36	Screw Term.	S4302	4044-1/Emergency Bldg. Lighting		12V	150			2 3/4"	Box	12	
30	PAR36	Screw Term.	S4303	4405/Spot Light		12.8V	100			2 3/4"	Box	12	
35	PAR36	Screw Term.	S4304	4406/Tractor, Flood		12.8V	300			2 3/4"	Box	12	
35	PAR36	Screw Term.	S4305	4411/Tractor		12.8V	300			2 3/4"	Box	12	
18	PAR36	Screw Term.	S4306	4414/Warning Signal, Emergency		12.8V	300			2 3/4"	Box	12	
35	PAR36	Screw Term.	S4307	4415/Fog		12.8V	300			2 3/4"	Box	12	
30	PAR36	Screw Term.	S4316	4416/Spotlamp, Signal		12.8V	100			2 3/4"	Box	12	
25	PAR36	Screw Term.	S4317	4446/Emergency Bldg. Lighting		12.8V	300			2 3/4"	Box	12	

Continued on next page

# Sealed Beam Lamps

## PAR36 & PAR46



**PAR46 Screw Terminal**

2 Piece Construction

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn./ Inner Pack
50	PAR36	Screw Term.	<b>S4318</b>	4502/Auto Headlamp, Military		28V	400			2 3/4"	Box	12
50	PAR36	Screw Term.	<b>S4319</b>	4505/Aircraft, Navigation		28V	400			2 3/4"	Box	12
100	PAR36	Screw Term.	<b>S4320</b>	4509/Aircraft, Landing, Spotlamp		13V	25			2 3/4"	Box	12
25	PAR36	Screw Term.	<b>S4321</b>	4510/Tractor, Flood, Emergency Bldg.		6.4V	300			2 3/4"	Box	12
30	PAR36	Screw Term.	<b>S4322</b>	4515/Spotlamp		6.4V	100			2 3/4"	Box	12
30	PAR36	Screw Term.	<b>S4323</b>	4516/Spotlamp		6.2V	100			2 3/4"	Box	12
0.50A	PAR36	Multi Term.	<b>S4324</b>	4546-1/Hand Lantern		4.75V	100			2 3/4"	Box	12
8	PAR36	Screw Term.	<b>S4325</b>	H7550/Hand Lantern, Halogen		6V	50			2 3/4"	Box	12
8	PAR36	Screw Term.	<b>S4326</b>	H7551/Emergency Bldg. Lighting, Halogen		6V	50			2 3/4"	Box	12
10	PAR36	Screw Term.	<b>S4327</b>	H7552/Emergency Bldg. Lighting, Halogen		6V	50			2 3/4"	Box	12
12	PAR36	Screw Term.	<b>S4328</b>	H7553/Emergency Bldg. Lighting, Halogen		6V	50			2 3/4"	Box	12
20	PAR36	Screw Term.	<b>S4329</b>	H7554/Emergency Bldg., Halogen		6V	50			2 3/4"	Box	12
8	PAR36	Screw Term.	<b>S4330</b>	H7555/Emergency Bldg. Lighting, Halogen		12V	50			2 3/4"	Box	12
6	PAR36	Screw Term.	<b>S4331</b>	H7556/Emergency Bldg. Halogen		6V	50			2 3/4"	Box	12
12	PAR36	Screw Term.	<b>S4332</b>	H7557/Emergency Bldg. Lighting, Halogen		12V	50			2 3/4"	Box	12
8	PAR36	Screw Term.	<b>S4333</b>	7613/Emergency Bldg. Lighting		6V	50			2 3/4"	Box	12
7.2	PAR36	Screw Term.	<b>S4334</b>	7672-1/Emergency Bldg. Lighting		6V	50			2 3/4"	Box	12
<b>PAR46</b>												
30	PAR46	Screw Term.	<b>S4335</b>	4435/Spotlamp		12.8V	100			2 3/4"	Box	12
30	PAR46	Screw Term.	<b>S4336</b>	4535/Spotlamp		6.4V	100			2 3/4"	Box	12



# Sealed Beam Lamps

## PAR56 & PAR64



**PAR56**  
**Mogul End Prong**

**2 Piece Construction**  
**120 Volt**

- S4668** 500 Watt Narrow Spot
- S4669** 500 Watt Med. Flood
- S4670** 500 Watt Wide Flood

Packing: Individually Boxed  
12/Master

**PAR64**  
**Mogul End Prong**

**2 Piece Construction**  
**120 Volt**

- S4671** 1000 Watt Narrow Spot
- S4672** 1000 Watt Med. Flood
- S4673** 1000 Watt Wide Flood

Packing: Individually Boxed  
12/Master

### Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Beam	Volts	Avg. Rated Hours	CBCP*	Lumens	Filament	M.O.L.	Pack. Type	Mst. Ctn.
500	PAR56	Mogul End Prong	S4668	500PAR56Q/NSP	Narrow Spot 8X15°	120V	4000	78500	8800	C,CC-6	5"	Box	12
500	PAR56	Mogul End Prong	S4669	500PAR56Q/MFL	Med.Flood 11X30°	120V	4000	40000	8800	C,CC-6	5"	Box	12
500	PAR56	Mogul End Prong	S4670	500PAR56Q/WFL	Wide Flood 20X45°	120V	4000	19500	8800	C,CC-6	5"	Box	12
1000	PAR64	Mogul End Prong	S4671	1000PAR64Q/NSP	Narrow Spot 18X20°	120V	4000	40000	19400	C,CC-6	6"	Box	6
1000	PAR64	Mogul End Prong	S4672	1000PAR64Q/MFL	Med.Flood 10X30°	120V	4000	82000	19400	C,CC-6	6"	Box	6
1000	PAR64	Mogul End Prong	S4673	1000PAR64Q/WFL	Wide Flood 20X60°	120V	4000	23000	19400	C,CC-6	6"	Box	6

sealed beam lamps

# Miniature Incandescent Lamps



Sub Miniature  
Wedge Base

Midget Flange  
Base

## T-1<sup>3</sup>/<sub>4</sub>

Indicator • Aircraft • Toy • Auto • P.C. Board

**S6900** #73 Sub Miniature Wedge Base

**S6901** #85 Sub Miniature Wedge Base

**S6902** #86 Sub Miniature Wedge Base

**S6903** #327 Midget Flange Base

**E387** #387 Midget Flange Base

Packing: 10 Bulbs/Sleeve



## T-2

Switch Board • Pilot  
Indicator

**Miniature  
Slide Base**

**S6904** #24PSB5

**E28PSB5** #28PSB5

**S6838** #48PSB5

**E120PSB5** #120PSB5

**S6841** #155PSB5

Packing: 10 Bulbs/Sleeve



## T-2<sup>1</sup>/<sub>2</sub>

Switch Board • Pilot  
Indicator

**Miniature  
Bayonet Base**

**E24MB** #24MB

**E28MB** #28MB

**S6844** #48MB

**S6905** #120MB

**E130MB** #130MB

**S6849** #155MB

Packing: 10 Bulbs/Sleeve

Not Shown Actual Size

Bulb Type	Base	Satco Order No.	Lamp Code	Amps	Volts	Avg. Rated Hours	Filament	M.O.L.	Mst. Ctn./ Inner Pack
T-1 <sup>3</sup> / <sub>4</sub>	Mini Wedge	<b>S6900</b>	73	.08	14V	15000	C-2F	.80"	10
T-1 <sup>3</sup> / <sub>4</sub>	Mini Wedge	<b>S6901</b>	85	.04	18V	7000	C-2F	.80"	10
T-1 <sup>3</sup> / <sub>4</sub>	Mini Wedge	<b>S6902</b>	86	.15	6.3V	20000	C-2F	.80"	10
T-1 <sup>3</sup> / <sub>4</sub>	Midget Flange	<b>S6903</b>	327	.04	28V	4000	C-2F	.80"	10
T-1 <sup>3</sup> / <sub>4</sub>	Midget Flange	<b>E387</b>	387	.04	28V	10000	C-2F	.625"	10
T-2	Slide	<b>S6904</b>	24PSB5	.073	24V	10000	C-2F	1.12"	10
T-2	Slide	<b>E28PSB5</b>	28PSB5	.04	28V	5000	C-2F	1.10"	10
T-2	Slide	<b>S6838</b>	48PSB5	.05	48V	10000	C-7A	1.10"	10
T-2	Slide	<b>E120PSB5</b>	120PSB5	.025	120V	10000	CC-7A	1.10"	10
T-2	Slide	<b>S6841</b>	155PSB5	.025	155V	10000	CC-7A	1.12"	10
T-2 <sup>1</sup> / <sub>2</sub>	Mini Bayonet	<b>E24MB</b>	24MB	.07	24V	10000	C-2F	1.19"	10
T-2 <sup>1</sup> / <sub>2</sub>	Mini Bayonet	<b>E28MB</b>	28MB	.04	28V	5000	C-2F	1.19"	10
T-2 <sup>1</sup> / <sub>2</sub>	Mini Bayonet	<b>S6844</b>	48MB	.053	48V	5000	C-7A	1.19"	10
T-2 <sup>1</sup> / <sub>2</sub>	Mini Bayonet	<b>E120MB</b>	120MB	.025	120V	10000	CC-7A	1.19"	10
T-2 <sup>1</sup> / <sub>2</sub>	Mini Bayonet	<b>E130MB</b>	130MB	.03	130V	10000	CC-7A	1.19"	10
T-2 <sup>1</sup> / <sub>2</sub>	Mini Bayonet	<b>S6849</b>	155MB	.025	155V	10000	CC-7A	1.19"	10

# Miniature

# *Incandescent* Lamps



Wedge Base

Min. Bay. Base

Mini Screw Base

**T-3 1/4**

Radio • Indicator • Auto

- |                                    |                                   |
|------------------------------------|-----------------------------------|
| <b>S6908</b> #40 Min. Screw Base   | <b>S6918</b> #755 Min. Bay. Base  |
| <b>S6909</b> #41 Min. Screw Base   | <b>S6919</b> #756 Min. Bay. Base  |
| <b>S6911</b> #46 Min. Screw Base   | <b>S6920</b> #757 Min. Bay. Base  |
| <b>S6913</b> #48 Min. Screw Base   | <b>S6856</b> #967 Min. Bay. Base  |
| <b>E1487</b> #1487 Min. Screw Base | <b>E1810</b> #1810 Min. Bay. Base |
| <b>E147</b> #147 Wedge Base        | <b>E1813</b> #1813 Min. Bay. Base |
| <b>S6914</b> #161 Wedge Base       | <b>E1815</b> #1815 Min. Bay. Base |
| <b>S6915</b> #168 Wedge Base       | <b>E1818</b> #1818 Min. Bay. Base |
| <b>E193</b> #193 Wedge Base        | <b>E1819</b> #1819 Min. Bay. Base |
| <b>S6916</b> #194 Wedge Base       | <b>E1820</b> #1820 Min. Bay. Base |
| <b>E400</b> #400 Wedge Base        | <b>E1829</b> #1829 Min. Bay. Base |
| <b>E464</b> #464 Wedge Base        | <b>E1835</b> #1835 Min. Bay. Base |
| <b>S6910</b> #44 Min. Bay. Base    | <b>E1864</b> #1864 Min. Bay. Base |
| <b>S6912</b> #47 Min. Bay. Base    |                                   |
| <b>S6917</b> #313 Min. Bay. Base   |                                   |

Packing: 10 Bulbs/Sleeve



**T-3**

Auto • Indicator

**D.E. Caps**

**S6906** #211-2

Packing:  
10 Bulbs/Sleeve



**TL-3**

Flashlight

**Mini Screw Base**

**S6907** #222

Packing:  
10 Bulbs/Sleeve

Not Shown Actual Size

Bulb Type	Base	Satco Order No.	Lamp Code	Amps	Volts	Avg. Rated Hours	Filament	M.O.L.	Mst. Ctn./ Inner Pack
T-3	D.E. Caps	<b>S6906</b>	211-2	0.97	12.8V	1000	C-8	1.72"	10
TL-3	Mini Screw	<b>S6907</b>	222	0.25	2.25V	5	C-2R	.93"	10
T-3 1/4	Mini Screw	<b>S6908</b>	40	0.15	6.3V	3000	C-2R	1.19"	10
T-3 1/4	Mini Screw	<b>S6909</b>	41	0.5	2.5V	3000	C-2R	1.19"	10
T-3 1/4	Mini Screw	<b>E1487</b>	1487	0.2	14V	500	C-2F	1.19"	10
T-3 1/4	Mini Screw	<b>S6911</b>	46	0.25	6.3V	3000	C-2R	1.19"	10
T-3 1/4	Mini Screw	<b>S6913</b>	48	0.06	2.0V	1000	C-6	1.19"	10
T-3 1/4	Wedge	<b>E147</b>	147	0.043	7V	1500	C-2R	1.06"	10
T-3 1/4	Wedge	<b>S6914</b>	161	0.08	14V	4000	C-2F	1.06"	10
T-3 1/4	Wedge	<b>E193</b>	193	0.033	14V	7500	C-2F	1.06"	10
T-3 1/4	Wedge	<b>S6915</b>	168	0.35	14V	1500	C-2F	1.06"	10
T-3 1/4	Wedge	<b>S6916</b>	194	0.27	14V	2500	C-2F	1.06"	10
T-3 1/4	Wedge	<b>E400</b>	400	0.1	28V	1000	C-2F	1.06"	10
T-3 1/4	Wedge	<b>E464</b>	464	0.17	28V	1500	C-2F	1.06"	10
T-3 1/4	Mini Bayonet	<b>S6910</b>	44	0.25	6.3V	3000	C-2R	1.19"	10
T-3 1/4	Mini Bayonet	<b>S6912</b>	47	0.25	6.3V	3000	C-2R	1.19"	10
T-3 1/4	Mini Bayonet	<b>S6917</b>	313	0.2	28V	500	C-2F	1.19"	10
T-3 1/4	Mini Bayonet	<b>S6918</b>	755	0.15	6.3V	20000	C-2R	1.19"	10
T-3 1/4	Mini Bayonet	<b>S6919</b>	756	0.08	14V	15000	C-2R	1.19"	10
T-3 1/4	Mini Bayonet	<b>S6920</b>	757	0.08	14V	15000	C-2R	1.19"	10
T-3 1/4	Mini Bayonet	<b>S6856</b>	967	0.02	130V	7000	CC-7A	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1810</b>	1810	0.4	6.3V	3000	C-2R	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1813</b>	1813	0.1	14.4V	1000	C-2V	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1815</b>	1815	0.2	14V	3000	C-2F	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1818</b>	1818	0.17	24V	250	C-2F	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1819</b>	1819	0.04	28V	2500	C-2F	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1820</b>	1820	0.1	28V	1000	C-2F	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1829</b>	1829	0.07	28V	1000	C-2F	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1835</b>	1835	0.05	55V	5000	C-2F	1.19"	10
T-3 1/4	Mini Bayonet	<b>E1864</b>	1864	0.17	28V	1500	C-2F	1.19"	10

miniature lamps

# Miniature *Incandescent* Lamps



**B-3 1/2**

Flashlight • Lantern  
**S.C. Min. Flange Base**

- S6921** #PR2
- S6922** #PR3
- S6923** #PR4
- S6924** #PR6
- S6925** #PR7
- S6926** #PR12
- S6927** #PR13
- S6928** #PR30

Packing:  
10 Bulbs/Sleeve



**G-3 1/2**

Flashlight • Bicycle • Indicator • Radio

- S6929** #10 Min. 2 Pin Base
- S6930** #12 Min. 2 Pin Base
- S6931** #14 Min. Screw Base
- S6932** #19 Min. 2 Pin Base
- S6933** #51 Min. Bay Base
- S6934** #53 Min. Bay Base

Packing:  
10 Bulbs/Sleeve



**G-4 1/4**

Toy • Lantern • Flashlight • Indicator

- S6935** #57 Min. Bay Base
- S6936** #425 Min. Screw Base
- S6937** #502 Min. Screw Base

Packing:  
10 Bulbs/Sleeve

*Not Shown Actual Size*

Bulb Type	Base	Satco Order No.	Lamp Code	Amps	Volts	Avg. Rated Hours	Filament	M.O.L.	Mst. Ctn./ Inner Pack
B-3 1/2	Flange	<b>S6921</b>	PR2	.50	2.38V	15	C-2R	1.25"	10
B-3 1/2	Flange	<b>S6922</b>	PR3	.50	3.57V	15	C-2R	1.25"	10
B-3 1/2	Flange	<b>S6923</b>	PR4	.27	2.33V	10	C-2R	1.25"	10
B-3 1/2	Flange	<b>S6924</b>	PR6	.30	2.47V	30	C-2R	1.25"	10
B-3 1/2	Flange	<b>S6925</b>	PR7	.30	3.70V	30	C-2R	1.25"	10
B-3 1/2	Flange	<b>S6926</b>	PR12	.50	5.75V	15	C-2R	1.25"	10
B-3 1/2	Flange	<b>S6927</b>	PR13	.50	4.75V	15	C-2R	1.25"	10
B-3 1/2	Flange	<b>S6928</b>	PR30	.86	3.75V	40	C-2R	1.25"	10
G-3 1/2	2 Pin	<b>S6929</b>	10	.300	2.47V	3000	C-6	.94"	10
G-3 1/2	2 Pin	<b>S6930</b>	12	.150	6.30V	5000	C-6	.94"	10
G-3 1/2	Mini Screw	<b>S6931</b>	14	.30	2.47V	15	C-2R	.94"	10
G-3 1/2	2 Pin	<b>S6932</b>	19	.10	14.4V	1000	C-6	.94"	10
G-3 1/2	Mini Bayonet	<b>S6933</b>	51	.220	7.5V	1000	C-2R	.94"	10
G-4 1/2	Mini Bayonet	<b>S6934</b>	53	.120	14.4V	1000	C-2V	.94"	10
G-4 1/2	Mini Bayonet	<b>S6935</b>	57	.24	14.4V	500	C-2V	1.06"	10
G-4 1/2	Mini Screw	<b>S6936</b>	425	.50	5.0V	15	C-2R	1.06"	10
G-4 1/2	Mini Screw	<b>S6937</b>	502	.15	5.1V	100	C-2R	1.06"	10

# Miniature *Incandescent* Lamps



S.C. Bayonet Base

D.C. Bayonet Base

## G-6

Auto • Indicator • Aircraft

- S6946** #63 S.C. Bayonet Base
- S6947** #67 S.C. Bayonet Base
- S6948** #89 S.C. Bayonet Base
- S6949** #90 D.C. Bayonet Base
- S6950** #97 D.C. Bayonet Base

Packing: 10 Bulbs/Sleeve



S.C. Bayonet Base

D.C. Bayonet Base

## B-6

Aircraft • Auto • Indicator

- S6951** #1003 S.C. Bayonet Base
- S6952** #1004 D.C. Bayonet Base

Packing: 10 Bulbs/Sleeve



## T-5

Auto • Indicator • Special • Service

### Mini Wedge Base

- S6938** #901
- S6939** #904
- S6940** #906
- S6941** #908
- S6942** #909
- S6943** #912
- S6944** #918
- S6945** #921
- E922** #922
- E939** #939

Packing: 10 Bulbs/Sleeve

Not Shown Actual Size

Bulb Type	Base	Satco Order No.	Lamp Code	Amps	Volts	Avg. Rated Hours	Filament	M.O.L.	Mst.Ctn./ Inner Pack
T-5	Mini Wedge	<b>S6938</b>	901	.31	12.8V	500	C-2R	1.49"	10
T-5	Mini Wedge	<b>S6939</b>	904	.69	13.5V	5000	C-2F	1.49"	10
T-5	Mini Wedge	<b>S6940</b>	906	.69	13.0V	1000	C-2F	1.49"	10
T-5	Mini Wedge	<b>S6941</b>	908	1.5	6.0V	50	C-2R	1.49"	10
T-5	Mini Wedge	<b>S6942</b>	909	.62	6.0V	50	C-2R	1.49"	10
T-5	Mini Wedge	<b>S6943</b>	912	1.0	12.8V	1000	C-2R	1.49"	10
T-5	Mini Wedge	<b>S6944</b>	918	.56	12.8V	500	C-2R	1.49"	10
T-5	Mini Wedge	<b>S6945</b>	921	1.4	12.8V	1000	C-2R	1.49"	10
T-5	Mini Wedge	<b>E922</b>	922	0.98	12.8V	200	C-2R	1.49"	10
T-5	Mini Wedge	<b>E939</b>	939	0.9	6V	200	C-6	1.49"	10
G-6	S.C. Bayonet	<b>S6946</b>	63	.63	7.0V	1000	C-6	1.44"	10
G-6	S.C. Bayonet	<b>S6947</b>	67	.59	13.5V	5000	C-6	1.44"	10
G-6	S.C. Bayonet	<b>S6948</b>	89	.58	13.0V	750	C-6	1.44"	10
G-6	D.C. Bayonet	<b>S6949</b>	90	.58	13.0V	750	C-6	1.44"	10
G-6	D.C. Bayonet	<b>S6950</b>	97	.59	13.5V	5000	C-6	1.44"	10
B-6	S.C. Bayonet	<b>S6951</b>	1003	.94	12.8V	200	C-6	1.75"	10
B-6	D.C. Bayonet	<b>S6952</b>	1004	.94	12.8V	200	C-6	1.75"	10

# Miniature Incandescent Lamps



D.C. Bay  
Base

S.C. Bay  
Base



Index  
Base

Plastic Wedge  
Base

## S-8

Auto • Aircraft • Indicator • Marine

**S6953** #88 D.C. Bayonet

**S6954** #93 S.C. Bayonet

**S6955** #1073 S.C. Bayonet

**S6966** #1141 S.C. Bayonet

**S6956** #1154 D.C. Index Base

**S6895** #1156 S.C. Bay

**S6896** #1156NA S.C. Bay

**S6957** #1157 D.C. Index Base

**S6958** #1157NA D.C. Index Base

**S6959** #2057 D.C. Index Base

**S6960** #2057NA D.C. Index Base

**S6961** #2357 D.C. Index Base

**S6962** #2357NA D.C. Index Base

**S6963** #3155 Plastic Wedge

**S6964** #3156 Plastic Wedge

**S6965** #3157 Plastic Wedge

Packing: 10 Bulbs/Sleeve

NA=Natural Amber Color



## RP-11

Auto • Lantern

**S6967**

#1133 S.C. Bayonet Base



Packing: 10 Bulbs/Sleeve

## Not Shown Actual Size

Bulb Type	Base	Satco Order No.	Lamp Code	Amps	Volts	Avg. Rated Hours	Filament	M.O.L.	Mst. Ctn./ Inner Pack
S-8	D.C. Bayonet	<b>S6953</b>	88	2.10	6.8V	300	C-6	2.00"	10
S-8	S.C. Bayonet	<b>S6954</b>	93	1.04	12.8V	700	C-6	2.00"	10
S-8	S.C. Bayonet	<b>S6955</b>	1073	1.8	12.8V	200	C-6	2.00"	10
S-8	D.C. Index	<b>S6956</b>	1154	2.63	6.4V	200	C-6	2.00"	10
S-8	SC. Bay	<b>S6895</b>	1156	2.63	12.8V	1200	C-6	2.00"	10
S-8	S.C. Bay	<b>S6896</b>	1156NA	2.63	12.8V	1200	C-6	2.00"	10
S-8	D.C. Index	<b>S6957</b>	1157	2.1	12.8V	1200	C-6	2.00"	10
S-8	D.C. Index	<b>S6958</b>	1157NA	2.1	12.8V	1200	C-6	2.00"	10
S-8	D.C. Index	<b>S6959</b>	2057	2.1	12.8V	1200	C-6	2.00"	10
S-8	D.C. Index	<b>S6960</b>	2057NA	2.1	12.8V	1200	C-6	2.00"	10
S-8	D.C. Index	<b>S6961</b>	2357	2.23	12.8V	400	C-6	2.00"	10
S-8	D.C. Index	<b>S6962</b>	2357NA	2.23	12.8V	400	C-6	2.00"	10
S-8	Plastic Wedge	<b>S6963</b>	3155	1.448	12.8V	1500	C-6	2.00"	10
S-8	Plastic Wedge	<b>S6964</b>	3156	2.1	12.8V	1200	C-6	2.00"	10
S-8	Plastic Wedge	<b>S6965</b>	3157	2.1	12.8V	1200	C-6	2.00"	10
S-8	S.C. Bayonet	<b>S6966</b>	1141	1.44	12.8V	1000	C-6	2.00"	10
RP-11	S.C. Bayonet	<b>S6967</b>	1133	3.91	6.1V	200	C-6	2.25"	10

# Miniature Xenon Lamps




			
<b>T-3 1/4</b>	<b>T-3 1/4</b>	<b>T5</b>	<b>T5</b>
Clear/12 Volt Wedge Base <b>S6968</b> 3 Watt <b>S6969</b> 5 Watt	Frosted/12 Volt Wedge Base <b>S6972</b> 5 Watt	Clear/12 Volt Wedge Base <b>S6978</b> 18 Watt	Frosted/12 Volt Wedge Base <b>S6981</b> 18 Watt
<b>T-3 1/4</b> Clear/24 Volt Wedge Base <b>S6974</b> 5 Watt <b>S6975</b> 7.5 Watt Packing: 10/Master	<b>T-3 1/4</b> Frosted/24 Volt Wedge Base <b>S6976</b> 5 Watt <b>S6977</b> 7.5 Watt Packing: 10/Master	<b>T5</b> Clear/24 Volt Wedge Base <b>S6979</b> 7.2 Watt <b>S6980</b> 10 Watt Packing: 10/Master	<b>T5</b> Frosted/24 Volt Wedge Base <b>S6982</b> 7.2 Watt <b>S6983</b> 10 Watt Packing: 10/Master

Not Shown Actual Size

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack Type	Mst. Ctn./ Inner Pack
3	T 3 1/4	Wedge	<b>S6968</b>	X3T3 1/4	Clear	12V	20000	15	C2V	1 1/16"	Box	10
5	T 3 1/4	Wedge	<b>S6969</b>	X5T3 1/4	Clear	12V	5000	33	C2V	1 1/16"	Box	10
5	T 3 1/4	Wedge	<b>S6974</b>	X5T3 1/4	Clear	24V	8000	38	C2V	1 1/16"	Box	10
5	T 3 1/4	Wedge	<b>S6972</b>	X5T3 1/4/F	Frosted	12V	5000	33	C2V	1 1/16"	Box	10
5	T 3 1/4	Wedge	<b>S6976</b>	X5T3 1/4/F	Frosted	24V	8000	38	C2V	1 1/16"	Box	10
7.5	T 3 1/4	Wedge	<b>S6975</b>	X7.5T3 1/4	Clear	24V	10000	65	C2V	1 1/16"	Box	10
7.5	T 3 1/4	Wedge	<b>S6977</b>	X7.5T3 1/4/F	Frosted	24V	10000	65	C2V	1 1/16"	Box	10
7.2	T5	Wedge	<b>S6979</b>	X7.2T5	Clear	24V	2500	68	C2R	1 1/2"	Box	10
7.2	T5	Wedge	<b>S6982</b>	X7.2T5/F	Frosted	24V	2500	68	C2R	1 1/2"	Box	10
10	T5	Wedge	<b>S6980</b>	X10T5	Clear	24V	2000	126	C2R	1 1/2"	Box	10
10	T5	Wedge	<b>S6983</b>	X10T5/F	Frosted	24V	2000	126	C2R	1 1/2"	Box	10
18	T5	Wedge	<b>S6978</b>	X18T5	Clear	12V	10000	250	C2R	1 1/2"	Box	10
18	T5	Wedge	<b>S6981</b>	X18T5/F	Frosted	12V	10000	250	C2R	1 1/2"	Box	10

# Miniature Xenon Lamps



T-3 1/4

Clear/12 Volt  
Festoon

S6985 5 Watt  
S6986 10 Watt

T-3 1/4

Clear/24 Volt  
Festoon

S6987 5 Watt  
S6988 10 Watt

Packing:  
10/Master



T-3 1/4

Frosted/12 Volt  
Festoon

S6989 5 Watt  
S6990 10 Watt

T-3 1/4

Frosted/24 Volt  
Festoon

S6991 5 Watt  
S6992 10 Watt

Packing:  
10/Master



RLX

Clear/12 Volt  
Rigid Loop

S6993 5 Watt  
S6994 10 Watt

RLX

Clear/24 Volt  
Rigid Loop

S6995 5 Watt  
S6996 10 Watt

Packing:  
10/Master



RLX

Frosted/12 Volt  
Rigid Loop

S6997 5 Watt  
S6998 10 Watt

RLX

Frosted/24 Volt  
Rigid Loop

S6999 5 Watt  
S6850 10 Watt

Packing:  
10/Master

Watts	Bulb Type	Base	Satco Order No.	Lamp Code	Finish	Volts	Avg. Rated Hours	Lumens	Filament	M.O.L.	Pack Type	Mst.Ctn./ Inner Pack
5	T 3 1/4	D.E. Cap	S6985	X5T3 1/4	Clear	12V	20000	50	C8	1 23/32"	Box	10
5	T 3 1/4	D.E. Cap	S6987	X5T3 1/4	Clear	24V	15000	50	C8	1 23/32"	Box	10
5	T 3 1/4	D.E. Cap	S6989	X5T3 1/4/F	Frosted	12V	20000	50	C8	1 23/32"	Box	10
5	T 3 1/4	D.E. Cap	S6991	X5T3 1/4/F	Frosted	24V	15000	50	C8	1 23/32"	Box	10
10	T 3 1/4	D.E. Cap	S6986	X10T3 1/4	Clear	12V	20000	120	C8	1 23/32"	Box	10
10	T 3 1/4	D.E. Cap	S6988	X10T3 1/4	Clear	24V	10000	120	C8	1 23/32"	Box	10
10	T 3 1/4	D.E. Cap	S6990	X10T3 1/4/F	Frosted	12V	20000	120	C8	1 23/32"	Box	10
10	T 3 1/4	D.E. Cap	S6992	X10T3 1/4/F	Frosted	24V	10000	120	C8	1 23/32"	Box	10
5	RLX	Rigid Loop	S6993	5RLX	Clear	12V	20000	45	C8	1 3/4"	Box	10
5	RLX	Rigid Loop	S6995	5RLX	Clear	24V	20000	40	C8	1 3/4"	Box	10
5	RLX	Rigid Loop	S6997	5RLX/F	Frosted	12V	20000	45	C8	1 3/4"	Box	10
5	RLX	Rigid Loop	S6999	5RLX/F	Frosted	24V	20000	40	C8	1 3/4"	Box	10
10	RLX	Rigid Loop	S6994	10RLX	Clear	12V	20000	100	C8	1 3/4"	Box	10
10	RLX	Rigid Loop	S6996	10RLX	Clear	24V	20000	100	C8	1 3/4"	Box	10
10	RLX	Rigid Loop	S6998	10RLX/F	Frosted	12V	20000	90	C8	1 3/4"	Box	10
10	RLX	Rigid Loop	S6850	10RLX/F	Frosted	24V	20000	90	C8	1 3/4"	Box	10

miniature lamps



# T8 Instant Start

## Electronic Ballast

### T8 Instant Start – Dedicated Voltage



#### <20% THD Electronic T8 Fluorescent Ballasts

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F32T8	1	120	S6623	QT1X32T8120/ISN/SC	10
F32T8	1	277	S6633	QT1X32T8277/ISN/SC	10
F32T8	2	120	S6624	QT2X32T8120/ISN/SC	10
F32T8	2	277	S6634	QT2X32T8277/ISN/SC	10
F32T8	3	120	S6625	QT3X32T8120/ISN/SC	10
F32T8	3	277	S6635	QT3X32T8277/ISN/SC	10
F32T8	4	120	S6626	QT4X32T8120/ISN/SC	10
F32T8	4	277	S6636	QT4X32T8277/ISN/SC	10

Also operates F17T8 • F25T8 • F28T8/SS • F30T8/SS • F40T8 • FBO16 • FBO24 • FBO31 • FBO 32  
For F40T8 operation, use 2 lamp ballast for 1 lamp, 3 lamp ballast for 2 lamps, 4 lamp ballast for 3 lamps.

F96T8	1/2	120	S5211	QT2X59120/IS	10
F96T8	1/2	277	S5212	QT2X59277/IS	10

Also Operates: FBO32, F025, FBO24, F017, FBO16, F030/SS, FBO30/SS, (30W Lamps) & F028/SS (28W Lamps)

### T8 Instant Start – Universal Voltage



#### <10% THD Electronic T8 Fluorescent Ballasts

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F32T8	1	120/277	S5207	QTP1X32T8/UNV/ISN/SC	10
F32T8	2	120/277	S5208	QTP2X32T8/UNV/ISN/SC	10
F32T8	3	120/277	S5209	QTP3X32T8/UNV/ISN/SC	10
F32T8	4	120/277	S5210	QTP4X32T8/UNV/ISN/SC	10

Also operates F17T8 • F25T8 • F28T8/SS • F30T8/SS • F40T8 • FBO16 • FBO24 • FBO31 • FBO32  
For F40T8 operation, use 2 lamp ballast for 1 lamp, 3 lamp ballast for 2 lamps, 4 lamp ballast for 3 lamps.

F96T8	2	120/277	S5213	QTP2X59T8/UNV/ISN/SC	10
-------	---	---------	-------	----------------------	----

Also Operates: FBO32, FBO31, F025, FBO24, F017, FBO16, F030/SS, FBO30/SS (30W Lamps) & F028/SS (28W Lamps)

### T8 4 Foot Programmed Start Universal Voltage



#### < 10% THD Electronic T8 Fluorescent Ballasts

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F32T8	1	120/277	S5286	QTP1X32T8/UNV/PSNTC	10
F32T8	2	120/277	S5287	QTP2X32T8/UNV/PSNTC	10
F32T8	3	120/277	S5288	QTP3X32T8/UNV/PSNTC	10
F32T8	4	120/277	S5289	QTP4X32T8/UNV/PSNTC	10

Also operates F17T8 • F25T8 • F28T8/SS • F30T8/SS • FBO16 • FBO24 • FBO31 • FBO32

Also Operates: F096T8/SS (55W Lamp)

# Electronic Ballasts



## T5 Programmed Start Universal Voltage

### T5 Programmed Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F28T5	1	120/277	<b>S5221</b>	QTP1X28UNVPSNNL	20
F28T5	2	120/277	<b>S5222</b>	QTP2X28UNVPSNNL	20

Also operates F14T5 • F21T5 • F35T5



### T5 HO Programmed Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F39T5/HO	1	120/277	<b>S5214</b>	QTP1X39/24T5HOUNVPSNNL	20
F39T5/HO	2	120/277	<b>S5215</b>	QTP2X39/24T5HOUNVPSNNL	20
Also operates F24T5/HO • FPC22 • FPC40 • FT24DL • CF24DF • FT36DL • CF36DF					
F54T5/HO	1	120/277	<b>S5218</b>	QTP1X54T5HOUNVPSNNL	20
F54T5/HO	2	120/277	<b>S5219</b>	QTP2X54T5HOUNVPSNNL	20
Also operates FT55DL • FPC55					
F80T5/HO	1	120/277	<b>S5220</b>	QTP1X80T5HOUNVPSNNL	20
Also operates FT80DL					



## 40 T12 Rapid Start

### T12 F40T12 Rapid Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F40T12	1	120	<b>S5258</b>	QTP1X40T12/120/RSN/B	20
F40T12	1	277	<b>S5259</b>	QTP1X40T12/277/RSN/B	20
F40T12	2	120	<b>S5260</b>	QTP2X40T12/120/RSN/B	20
F40T12	2	277	<b>S5261</b>	QTP2X40T12/277/RSN/B	20
F40T12	3	120	<b>S5262</b>	QTP3X40T12/120/RSN/B	20
F40T12	3	277	<b>S5263</b>	QTP3X40T12/277/RSN/B	20



# Electronic Ballasts

## TT5 Instant Start



### TT5 FT40DL Instant Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
FT40	1	120	S5240	QT1x40/120/DL	10
FT40	1	277	S5241	QT1x40/277/DL	10
FT40	2	120	S5242	QT2x40/120/DL	10
FT40	2	277	S5243	QT2x40/277/DL	10
FT40	3	120	S5244	QT3x40/120/DL	10
FT40	3	277	S5245	QT3x40/277/DL	10

## Compact Fluorescent



Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
CF13	1/2	120/277	S5223	OTP1/2X13CF/UNV/BS	20
CF13	1/2	120/277	S5225	OTP1/2X13CF/UNV/TS	20
Operates 1 or 2 each CF13DT/E • CF13DD/E					
CF18	1/2	120/277	S5226	OTP1/2X18CF/UNV/BS	20
CF18	1/2	120/277	S5228	OTP1/2X18CF/UNV/TS	20
Operates 1 or 2 each CF18DT/E • CF18DD/E					
CF26	1/2	120/277	S5229	OTP1/2X26CF/UNIV/BS	20
CF26	1/2	120/277	S5231	OTP1/2X26CF/UNIV/TS	20
Operates 1 or 2 each CF26DT/E • CF26DD/E Operates 1 each CF32DT/E • CF42DT/E					
CF26	1/2	120/277	S5232	OTP1/2XCF/UNV/BM	20
CF26	1/2	120/277	S5233	OTP1/2XCF/UNV/PM	18
CF26	1/2	120/277	S5234	OTP1/2XCF/UNV/TM	18
Operates 1 or 2 each CF26DT/E • CF26DD/E Operates 1 each CF32DT/E • CF42DT/E					
CF26	2	120/277	S5235	OTP2X26/32/42CF/UNIV/BM	20
CF26	2	120/277	S5236	OTP2X26/32/42CF/UNIV/PM	18
CF26	2	120/277	S5237	OTP2X26/32/42CF/UNIV/TM	18
Operates 2 each CF26DT/E • CF32DT/E • CF42DT/E					
CF57	1	120/277	S5238	OTP1X57CF/UNV/BM	20
CF57	1	120/277	S5239	OTP1X57CF/UNV/PM	18
Operates 1 each CF57DT/E • CF70DT/E					

BS = Bottom Mount / Plastic Case  
 TS = Top Mount / Plastic Case  
 BM = Bottom Mount / Metal Case  
 PM = PEM Stud Mount / Metal Case  
 TM = Top Mount / Metal Case

## T2 Universal Voltage



### T2 Subminiature

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
FM13	1/2	120/277	S5246	QT-FM	50
Operates 1 or 2 FM6 • FM8 • FM11 • FM13					

# Magnetic Ballasts

## Rapid Start

### F40T12 & F34T12 Rapid Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F34T12	1	120	S5274	MB1X40/120RS	10
F34T12	1	277	S5275	MB1X40/277RS	10
Also operates F40T12 • F40T10 • FB40T12 • FB34T12/SS • F30T12 • F25T12/SS					
F34T12	2	120	S6620	MB2X40/120RS	10
F34T12	2	277	S6622	MB2X40/277RS	10
Also operates F40T12 • F40T10 • FB40T12 • FB34T12/SS					
F40T12	1	120	S5276	MB1X40/120RES	16
Operates F40T12 FULL WATTAGE LAMPS ONLY - Not for use for F34T12 lamps					
F30T12	2	120	S5171	MB2X30/120RS	10
F30T12	2	277	S5170	MB2X30/277RS	10
Operates F30T12 and F25T12/SS Lamps					



## Instant Start Slimline

### T12 Slimline Instant Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F48T12	2	120	S5277	MB2X48/120IS	6
F48T12	2	277	S5278	MB2X48/277IS	6
Also operates F48T12/SS					
F96T12	1	120	S5279	MB1X96/120IS	6
F96T12	1	277	S5280	MB1X96/277IS	6
F96T12	2	120	S6621	MB2X96/120IS	6
F96T12	2	277	S5281	MB2X96/277IS	6
Also operates F60T12 • F64T12 • F72T12 • F84T12 • F96T12/SS					



## Preheat/Trigger Start

### T8 / T12 PreHeat and Trigger Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F15T12	1	120	S5268	MB1X15/120PH/TP	16
F20T12	1	120	S5269	MB1X20/120PH/TP	40
F20T12	1	120	S5270	MB1X20/120PH	40
F20T12	2	120	S5271	MB2X20/120PH/TP	16
Also operates F14T8 • F14T12 • F15T8 • F15T12					

TP = Thermal Protection



# Magnetic

## Ballasts

### Circline



#### T9 Circline Rapid Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
FC8T9	1	120	S5273	MB1X22/120CIRC	16
FC12T9	1	120	S5272	MB1X32/120CIRC	16

Also operates FC16T9

### Rapid Start HO



#### T12 HO Rapid Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F96T12/HO	1	120	S5282	MB1X96HO/120RS	4
F96T12/HO	1	277	S5283	MB1X96HO/277RS	4
F96T12/HO	2	120	S5284	MB2X96HO/120RS	4
F96T12/HO	2	277	S5285	MB2X96HO/277RS	4

Also operates F24HO • F36HO • F42HO • F48HO • F60HO • F72HO • F84HO • F96HO/SS

### Rapid Start VHO



#### T12 VHO Rapid Start

Primary Lamp Type	Number of Lamps	Voltage	Satco Order No.	Ballast Number	Case
F96T12/VHO	1	120	S5264	MB1X96/VHO/120RS	4
F96T12/VHO	1	277	S5265	MB1X96/VHO/277RS	4

Also operates F48/VHO • F60/VHO • F72/VHO • F96/VHO/SS

F96T12/VHO	2	120	S5266	MB2X96/VHO/120RS	4
F96T12/VHO	2	277	S5267	MB2X96/VHO/277RS	4

Also operates F72/VHO • F96/VHO/SS

## Socket Ballasts Twist-Lock



### Socket Ballasts

- Finish: Ivory
- Rating: 120V/60HZ
- CUL Listed
- Rated: Indoor / Outdoor  
Minus 20 Degrees
- Replaceable
- Detachable:  
Twist Lock Socket



13/18/26W  
Standard



13/18/26W Uno Ring  
Standard with Uno Ring

80-1325 13W  
80-1324 18W  
80-1383 26W

80-1335 13W  
80-1336 18W  
80-1382 26W



26/32/42W  
Multi-Wattage



26/32W/Dimming  
Multi-Wattage



13/18/26W  
Low Profile

80-1323

80-1331  
• Integral Harp Saddle  
• Integral Dimmer  
• Indoor Only

80-1384 13W  
80-1385 18W  
80-1386 26W

Primary Lamp Type	Satco OrderNo.	Finish	Terminal	Cap	Hickey	Wire	Pkd
13W	80/1325	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
18W	80/1324	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
26W	80/1383	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
13W Uno / Ring	80/1335	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
18W Uno / Ring	80/1336	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
26W Uno / Ring	80/1382	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
26/32/42 W	80/1323	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
26/32 Dimmer	80/1331	Ivory	With 36" Leads	Cap	Hickey	UL1015	200
13W Small	80/1384	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
18W Small	80/1385	Ivory	With 24" Leads	Cap	Hickey	UL1015	200
26W Small	80/1386	Ivory	With 24" Leads	Cap	Hickey	UL1015	200

## SATCO BULB CHANGERS

The easy way to change hard to reach bulbs. Available in PAR, incandescent and R type changers.

Not Shown  
Actual Size



Incandescent  
Bulb Changer  
**S70-0101**



Par Type  
Bulb Changer  
**S70-3001**



R Type  
Bulb Changer  
**S70-3002**



**90-1310**

Brass Finish  
Light Bulb Cage  
(for use with 90-445  
keyless receptacle)



**92-324**

Medium to Medium  
Porcelain  
Extender  
Overall Ext. 1"



**92-323**

Medium to Medium  
Bakelight  
Extender  
Overall Ext. 1"



8-24 Ft. ▶

### Alumiglass Extension Pole

**S70-6624**

Two section handle,  
threaded end fits  
all changers.  
Professional quality.

8-16 Ft. ▶

### Alumiglass Extension Pole

**S70-6516**

Two section handle,  
threaded end fits  
all changers.  
Professional quality.

*Note:* For standard  
ceilings, broomstick  
handle will fit changers.

◀ 6-12 Ft.

### Aluminum Extension Pole

**S70-9272**

Two section handle,  
"nylon" threaded,  
fits all changers.  
Homeowner quality.



accessories



**S1352 Four foot display canopy**

22" D X 48" W X 10" H

The bold colors and contemporary graphics of this dynamic header create a sophisticated product presentation. The 22" X 48" bottom Chrome louver allows light to pass through for product illumination.

Mounts to any standard four foot gondola display.

**Four Color Retail Packaging**

offers ease of product identification, uniformity and contemporary design.

Many of our items are packaged in four color inner cartons. These multi-packs can be stacked out for promotional purposes creating additional sales!



merchandising







*Satco Light Bulbs - A brand consumers have purchased with confidence for over 40 years.*



merchandising

*S1300 A - Four foot white gondola display. (Bottom shelf included)  
48"W X 24"D X 71"H*

*S1300 B - (3) Four foot white shelves*





*Satco Power Panels can be mounted on the end of a gondola display or hung on a wall.*

merchandising



**S1360** *Decorative light bulb power panel:*

- 10 - S3774      10 - S3786
- 10 - S3782      10 - S3732
- 10 - S3778      10 - S3735
- 10 - S3785      10 - S3762
- 10 - S3731      10 - S3784
- 10 - S3734      10 - S3763
- 10 - S3775      10 - S3787
- 10 - S3783      10 - S3793
- 10 - S3779      10 - S3796

15"W X 48"H X 4.5"D



**S1361** *Appliance light bulb power panel:*

- 10 - S3708      20 - S3724
- 10 - S3712      20 - S3797
- 20 - S3720      10 - S3711
- 20 - S3723      10 - S3703
- 20 - S3792      20 - S3729
- 10 - S3709      20 - S3791
- 10 - S3702      20 - S3794
- 20 - S3721

15"W X 48"H X 4.5"D



**S1362** *Halogen light bulb power panel:*

- 12 - S3459      12 - S3486
- 12 - S3468      12 - S3432
- 12 - S3469      12 - S3488
- 12 - S3465      12 - S3489
- 12 - S3467      12 - S3431
- 12 - S3425      12 - S3496
- 12 - S3461      12 - S3497
- 12 - S3462      12 - S3480
- 12 - S3463      12 - S3481
- 12 - S3484      12 - S3423
- 12 - S3485

15"W X 48"H X 4.5"D

## Halogen Light Bulb Center 2' MERCHANDISING PROGRAM

- Self Stocking Display Unit
  - High Impact Graphics & Packaging
    - Adjustable Shelves
  - Uses Only 2'X2' Floor Space
  - Features; Soft Ray Glare Free MR16 & PAR Lamps
- Plus Other Halogen Up Sell Products

#HAL/2FT/DISP

### Counter Top Demonstrator Display



S1410 Soft Ray demonstrator

Interactive display unit compares a standard halogen lamp to a Soft Ray frosted PAR

14 1/2" W X 13 3/4" D X 18 1/2" H



Halogen Light Bulb Center:

6 - S4603	24 - S4503	15 - S4103
6 - S4600	24 - S4504	15 - S4104
6 - S4601	12 - S4120	15 - S4105
6 - S4602	12 - S4121	15 - S4106
12 - S4500	12 - S4122	15 - S4107
12 - S4501	12 - S4123	1 - S4150
12 - S4502	15 - S4100	1 - S4152
12 - S4505	15 - S4101	
12 - S4506	15 - S4102	

Actual Dimensions: 27" W X 76" H



## SATCO'S

POINT of PURCHASE  
DISPLAYS are the perfect tool to assist in the promotion of Satco brand lighting products.

## Energy Saving Light Bulb Center

### 2' MERCHANDISING PROGRAM

- Self Stocking Display Unit
- High Impact Graphics & Packaging
- Adjustable Shelves
- Uses Only 2'X2' Floor Space
- Features; Energy Star Certified Products

#CFL/2FT/DISP



### Energy Saving Light Bulb Center:

12 - S6202*	12 - S6214*	6 - S6244
12 - S6203*	12 - S6215*	12 - S6245
12 - S6204*	6 - S6216*	6 - S6253
6 - S6210	6 - S6217	6 - S6254
6 - S6211*	6 - S6218*	1 - S1415
6 - S6212*	6 - S6222	1 - S1453
12 - S6213*	12 - S6243	

Actual Dimensions: 27" W X 76" H

## Light Bulb Center

### 2' MERCHANDISING PROGRAM

- Self Stocking Display Unit
- High Impact Graphics & Packaging
- Adjustable Shelves
- Uses Only 2'X2' Floor Space

#GEN/2FT/DISP

#### Light Bulb Center:

48 - S1711	24 - S2808
48 - S1712	24 - S2809
48 - S1713	12 - S4421
48 - S1714	12 - S4426
48 - S1810	24 - S2853
48 - S1811	24 - S2854
48 - S1812	24 - S2855
36 - S1820	20 - S3791
36 - S1821	20 - S3792
24 - S3938	20 - S3729
12 - S3440	20 - S3724
12 - S3441	20 - S3720
12 - S3442	20 - S3721
12 - S3443	10 - S3703
12 - S3447	10 - S3705
12 - S3448	10 - S3778
12 - S3449	10 - S3779
24 - S3204	10 - S3754
24 - S3211	10 - S3728

Actual Dimensions: 27" W X 76" H





## Decorative Bulb Displays

- Gravity feed bulb dispenser
- Stocks 24 different styles
- Compact size
- Versatile merchandising options
- Contemporary design
- Easy product identification



**S-101** Wall mounted decorative light bulb display.

Stocks the same product selection as the S-100 merchandiser.

45"L X 27"H X 6.6"D




Rotating Display can be used free standing, or countertop

### **S-100 DISPLAY**

This self-standing floor or counter display takes up less than 2sq. ft. of space.

S-100 display consists of rack and 25ea. of:  
S3231, S3232, S3234, S3235, S3262, S3263, S3273, S3274, S3275, S3277, S3278, S3279, S3282, S3283, S3284, S3285, S3286, S3287, S3293, S3296, S3822, S3823, S3825 & S3826

Floor display 66" H.



Counter display 40" H.

merchandising

## Light Bulb Center Promotional Signs

### Hanging and Window

**S1462** Hanging  
3-Way Sign  
Includes; string and hook  
for hanging



**S1461** Window/Hanging  
2-Way Signs  
Includes; string, hook & suction cups  
for hanging and window use