


ACCESSORIES

Accessories for Nora Recessed Fixtures




NR-30 5/8" Plastic
NOR-30 7/8" Plastic
NMR-30 5/8" Metal
NMOR-30 7/8" Metal
Designer Trim Rings
 Standard & oversize rings for use with 6" trims
 Finishes: W, B, C, G



NR-401 5/8"
NOR-401 7/8"
Designer Trim Rings
 Standard & oversized metal rings for use with 4" trims
 Finishes: W, B, C, G



NRA-13 24"
NRA-28 27" flat
Bar Hangers
 Adjustable & flat bar hangers for Nora housings



NRA-38
Channel Bar Hangers
 Bar hanger for Architectural Fluorescent Housings




NRA-10
Socket Extender
 Allows use of a short neck lamp where long neck is desired




NRA-14
Socket with Thermal Protector
 Replacement socket with thermal protector for Nora incandescent housings



NSC-6500
6" Maximum Adjustable Hole Cutter
NSC-6600
8" Maximum Adjustable Hole Cutter
 Hole cutter for 7/8" (23mm) drywall, plywood, plaster, or acrylic. May cut 1-3/4" (45mm) with above ceiling access. May also cut 1/16" (1.6mm) aluminum, brass, or sheet metal. Includes catch tray for shavings. Protective eyewear recommended.




NRA-37
Halogen Retrofit Kit
 Halogen retrofit kit/line voltage with MR16 GU 8.0 lamp base
 Lamp: 45W included




NRA-29
NRA-29/75
Transformer
 Transformer converts 120V line voltage to 12V low voltage




NET-300/C2
Electronic Transformer
 Converts 120V to 12V. One transformer operates up to six 50VA fixtures NEC class II fused.



NRA-30 N.P.F.
NRA-31 H.P.F.
NRA-32 277V
NRA-33 H.P.F./277V
Fluorescent Ballast
 Fluorescent Ballast for one 13W / 18W



NM-100F Frosted
NM-100S Spread
NM-100L Linear Spread
NM-100B Blue
NM-100Y Yellow
NM-100G Green
NM-100R Red
NM-100P Pink
Filters
 Filters for use with MR16



NRA-34 6", No Shield, 12V GU 5.3
NRA-34L 6", No Shield, 120V GU 8.0
NRA-35 18", Shielded, 12V GU 5.3
NRA-36 24", Shielded, 12V GU 5.3
MR16 Socket Leads



NRA-11
Eyeball Adapter
 For use with Eyeball and Adjustable trims