

June 2016 Dallas Market



QUOIZEL.  
*Artisans in Lighting...since 1930*



## TITLE 24 COMPLIANT ENERGY-EFFICIENT

- 13W, 18W or 23W Compact Fluorescent Included
- CFL Spring Self-Ballasted GU 24

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying this logo. (Medium base bulbs only)



## DIFFUSER INCLUDED



## DAMP LOCATION



## WET LOCATION



## MOUNTS AS UPLIGHT OR DOWNLIGHT



## MOUNTS VERTICALLY OR HORIZONTALLY



### DIMMERS:

Integrated Low Voltage LED Fixture – requires Electronic Low Voltage (ELV) dimmer.

Integrated 120v LED Fixture – C-L Dimmers recommended.

For more specific dimmer information, please contact: [engineering@quozel.com](mailto:engineering@quozel.com).

### WARRANTY:

Please refer to [Quozel.com](http://Quozel.com) for complete warranty information.



### Bulbs:

- Bulbs not included unless otherwise noted.
- Vintage Bulbs supplied are not necessarily the maximum wattage allowed.
- Products using LED and Halogen bulbs come with bulb(s) supplied in carton.
- Wattages stated are the maximum recommended; however, you may use lower wattages to suit your lighting needs.

### LED:

- Integrated LED information chart provided wherever applicable.

### Chain:

- (Single Tier) Chandelier, Dinette, Mini Chandeliers, Pendants, Mini Pendants and Island Lights come with 8' of wire and 4' of chain.
- (Two & Three Tier) Chandeliers and Foyer Fixtures come with 12' of wire and 8' of chain.
- All Outdoor Hanging Fixtures come with 12' of wire and 8' of chain.
- All Chain-Hung Mini Pendants come with 8' of wire and 4' of chain.

### Other:

- All Rod-Hung Mini Pendants come with a minimum of 8' of wire.
- All Cord-Hung Mini Pendants come with a minimum of 8' of cord.
- All Cable-Hung Mini Pendants come with a minimum of 8' of cable.

### Damp / Wet Locations:

- All flush and semi-flush mounted fixtures, bath fixtures and chandeliers are "Damp Location" listed.
- All outdoor hanging fixtures are "Damp Location" listed.
- All outdoor wall and post lights are "Wet Location" listed.

### Electrical:

- All electrical fixtures are rated at 120-volt AC unless otherwise noted.
- Unless specified, all electrical fixtures are cUL or ETL listed.

### Hardware:

- Backplate information and HCWO (Height from Center of Wall Opening) included for most wall fixtures (including outdoor) and bath fixtures.
- Canopy information included on almost all fixtures.
- All mirrors come with mounting hardware.

### Tiffany / Naturals:

- Glass color in Tiffany lighting products vary in color. No two pieces are identical.
- Products that use natural materials are perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.

### Glass / Shades:

- Will appear darker when not illuminated.

*In our efforts to constantly improve our products, changes may be made throughout the year that vary from printed information in the catalog.*

# June 2016 Dallas Market

**Photo Index..... 2 - 7**

**Quoizel Collections ..... 8 - 12**

**Platinum Collection ..... 13 - 23**

**Dining & Foyer..... 24 - 26**

**Track Lighting ..... 27**

**Pendants ..... 28 - 31**

**Semi-Flush & Flush Mounts ..... 32 - 33**

**Table & Floor ..... 34 - 44**

**Bath ..... 45 - 53**

**Outdoor ..... 54 - 59**

**Corporate Headquarters**

6 Corporate Parkway  
 Goose Creek, SC 29445  
 Phone: (843) 553-6700

**Corporate Headquarters  
 Customer Service**

590 Old Willets Path  
 Hauppauge, NY 11788  
 Phone: (631) 273-2700  
 Fax: (631) 231-7102  
 Toll-Free Consumer Hotline: (800) 645-5233


**Showrooms**

**Dallas Trade Mart**

3rd Floor, Space 3200  
 Dallas, TX 75207  
 Phone: (214) 747-3665

**High Point**

Showplace 3515  
 211 E. Commerce Avenue  
 High Point, NC 27260

© Quoizel, Inc. 

**QUOIZEL**

is a registered trademark of Quoizel ®, Inc.



# Quoizel Collections

photo index



**Belgrade 8 - 9**



**Trilogy 10 - 12**

# Platinum Collection

photo index



**Crescent 13**



**Enrapture 13**



**Blaze 14**



**Crystal Cove 14**



**Grotto 15**



**Pillar 15**



**Infinity 16**



**Abode 17**



**Legion 17**



**Verity 17**



**Luminous 18**



**Starlet 18**



# Platinum Collection

(continued)

photo index



Radiance 19



Sylvan 19



Aglow 20



Lunette 20



Axis 21



Baton 21



Fantasy 22



Promenade 22



Evermore 23



Gala 23



Paragon 23

# Dining & Foyer

photo index



Kyle 24



Berwick 25



Denton 25



Riverton 25



Afton 26



Brightwaters 26




Fort Quinn 26

# Track Lighting

photo index



Cinema 27



Theater 27

# Pendants

photo index



Avondale 28



Spiral 28



Cambria 29



Landings 29



Boutique 30



Portal 30



Boundary 31

# Semi Flush & Flush

photo index



Alexandria 32



Moon Rays 32



Westchester 32



Whitecap 32



Avondale 33



Boundary 33



Landings 33



Victory 33

# Table & Floor

photo index



**Flowing Heart 34**



**Jungle Dragonfly 34**



**Red Maple 34**



**Cobalt 35**



**Persian Violet 35**



**Royal Briar 35**



**Craft 36**



**Hideaway 36**



**Landings 36**



**Spirit 36**



**Theory 36**



**Chester 37**



**Elliot 37**



**Maze 38**



**Smokey Pearl 38**



**Stride 38**



# Table & Floor

(continued)

photo index



**Artic 39**



**Lakeshore 39**



**Riverfront 39**



**Overlook 40**



**Stargaze 40**



**Clift 41**



**Millington 42**



**Alfred 43**



**Bradford 43**



**Bridge 43**



**Vane 43**



**Crossway 44**



**Edge 44**



**Incline 44**



**Venton 44**

# Bath Fixtures

photo index



**Weave 45**



**Kolt 46 - 47**



**Banner 47**



**Arch 48**



**Trilogy 49**



**Andrews 50**



**Highfield 51**



**Taylor 52**



**Nicholas 53**

# Outdoor Fixtures

photo index



**Beacon 54 - 55**



**Livingston 56 - 57**



**Stonington 58**



**Malibu 59**

**FINISH:** Western Bronze

Simple and unadorned, the Belgrade Collection is a perfectly understated design. You can catch a glimpse of the vintage filament bulbs through the grill-like styling of the barred shade. The western bronze finish on the open-strap arms and fixture body coordinates well with many existing finishes.



**DAMP** **BGD5006WT**







DAMP

BGD1716WT

VINTAGE STYLE  
bulb included



DAMP

BGD2820WT



DAMP

BGD5203WT

## Belgrade collection

ITEM	DIMENSIONS	CANOPY	BULBS
BGD1716WT	13.5" H, 16.5" W, 16.5" Dp.	1.5" x 6.5"	3-60W Vintage Bulb (Supplied)*
BGD2820WT	25.5" H, 20.5" W, 20.5" Dp.	1.5" x 5"	4-60W Vintage Bulb (Supplied)*
BGD5006WT	25.5" H, 28" W, 28" Dp.	1.5" x 5"	6-60W Vintage Bulb (Supplied)*
BGD5203WT	26" H, 15.5" W, 15.5" Dp.	1.5" x 5"	3-60W Vintage Bulb (Supplied)*

Chain-hung fixtures come with 8' of wire & 4' of chain. \*MAX WATTAGE: 100W Med. Base or 23W CFL.

# TRILOGY

collection

**FINISH:** Brushed Nickel

**GLASS:** Clear Seedy

Trilogy pays homage to Thomas Edison with a vintage inspired filament bulb that is not only nostalgic but also very chic. With the brushed nickel finish and the clear seedy glass shade Trilogy brings old world style to modern elegance. On trend and classy.



DAMP

TRG1508BN

DAMP

TRG8701BN



DAMP

TRG5105BN

**DAMP****TRG1712BN****DAMP****TRG1716BN**
**VINTAGE STYLE**  
 bulb included
**DAMP****TRG5103BN****DAMP****TRG1816BN**

# Trilogy collection

ITEM	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TRG1508BN	7.5" H**, 8" W, 8" Dp.	1" x 5"	-	1-60W Vintage Bulb (Supplied)*
TRG1712BN	10" H, 12" W, 12" Dp.	1" x 5"	-	1-60W Vintage Bulb (Supplied)*
TRG1716BN	12" H, 16" W, 16" Dp.	1" x 5"	-	3-60W Vintage Bulb (Supplied)*
TRG1816BN	20" H, 16" W, 16" Dp.	1" x 5"	-	3-60W Vintage Bulb (Supplied)*
TRG5103BN	16.5" H, 22" W, 22" Dp.	1" x 5"	-	3-60W Vintage Bulb (Supplied)*
TRG5105BN	18.5" H, 26.5" W, 26.5" Dp.	1" x 5"	-	5-60W Vintage Bulb (Supplied)*
TRG8701BN	9.5" H, 8" W, 9" Dp.	1" x 5"	3"	1-60W Vintage Bulb (Supplied)*

Chain-hung fixtures come with 8' of wire & 4' of chain. \*MAX WATTAGE: 100W Med. Base or 23W CFL.  
 All rod-hung fixtures come with 10' of wire. \*\*Comes with (2) 6" and (2) 12" Rods.



# TRILOGY

collection

**FINISH:** BN - Brushed Nickel  
OZ - Old Bronze

**GLASS:** Clear Seedy

**DAMP** TRG8602BN



**DAMP** TRG8603BN



**DAMP** TRG8604BN



## MOUNTS

**DAMP** TRG8602OZ



**DAMP** TRG8603OZ



**DAMP** TRG8604OZ



## Trilogy collection

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
TRG8602BN/OZ	8.5" H, 17.5" W, 9" Dp.	4.5" x 8"	4.25"	2-60W Vintage Bulb (Supplied)*
TRG8603BN/OZ	8.5" H, 26.5" W, 9" Dp.	4.5" x 8"	4.25"	3-60W Vintage Bulb (Supplied)*
TRG8604BN/OZ	8.5" H, 36.5" W, 9" Dp.	4.5" x 8"	4.25"	4-60W Vintage Bulb (Supplied)*

**DAMP** PCCN2824PK

## Crescent

**FINISH:** Polished Nickel



Detail



**DAMP** PCCN2818PK

PLATINUM  
by QUOIZEL



## Enrapture

**FINISH:** Polished Chrome

**DAMP** PCER1718C

Detail



ITEM	DIMENSIONS	CANOPY	BULBS
PCCN2818PK	13" H*, 18" W, 18" Dp.	6"	4-60W Cand. Base
PCCN2824PK	13" H*, 24.5" W, 24.5" Dp.	6"	6-60W Cand. Base
PCER1718C	13" H, 18" W, 18" Dp.	1.75" x 13.75"	8-20W Clear G4 Xenon

All rod-hung fixtures come with 10' of wire. \*Comes with (2) 6" and (2) 12" Rods.

Detail



**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	2,200
Total Watts	22W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

**DAMP** **PCBZ1616C**



## Blaze

**FINISH:** Polished Chrome

**GLASS:** Crystal Accents

**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	1,700
Total Watts	17W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



**DAMP** **PCBZ1612C**

**PLATINUM**  
by QUOIZEL

**DAMP** **PCCC1614C**



## Crystal Cove

**FINISH:** Polished Chrome

**GLASS:** Crystal Accents

**DAMP** **PCCC1814C**



ITEM	DIMENSIONS	CANOPY	BULBS/LIGHT SOURCE
<b>PCBZ1612C</b>	2" H, 12.5" W, 12.5" Dp.	2" x 11"	See Chart for LED Information
<b>PCBZ1616C</b>	2.5" H, 16" W, 16" Dp.	-	See Chart for LED Information
<b>PCCC1614C</b>	7.5" H, 13.5" W, 13.5" Dp.	1" x 11"	4-40W Clear G9 Xenon (Supplied)
<b>PCCC1814C</b>	9.5" H, 13.5" W, 13.5" Dp.	1" x 4.75"	4-40W Clear G9 Xenon (Supplied)



Convertible to Semi-Flush



**DAMP** ■ **PCGO1616C**

## Grotto

**FINISH:** Polished Chrome

**SHADE:** Laser-cut Metal with Hanging Inner Crystals



**DAMP** ■ **PCGO1816C**

← *dangling crystals*

Convertible to Semi-Flush



**DAMP** ■ **PCGO1822C**



**DAMP** ■ **PCPI1815C**

→ *LED lights on arms*



**PLATINUM**  
by QUOIZEL

**INTEGRATED LED**  
10 YEAR WARRANTY

## Pillar

**FINISH:** Polished Chrome

**GLASS:** Crystal Ball Accents

### LED CHART

Lumens	2,250
Total Watts	22.5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

ITEM	DIMENSIONS	CANOPY	BULBS/LIGHT SOURCE
<b>PCGO1616C</b>	7.5" H, 16" W, 16" Dp.	1" x 14.75"	6-40W Clear G9 Xenon (Supplied)
<b>PCGO1816C</b>	8" H*, 16" W, 16" Dp.	1" x 4.75"	6-40W Clear G9 Xenon (Supplied)
<b>PCGO1822C</b>	9" H*, 21.5" W, 21.5" Dp.	1" x 4.75"	8-40W Clear G9 Xenon (Supplied)
<b>PCPI1815C</b>	16" H, 15" W, 15" Dp.	2.75" x 5"	See Chart for LED Information

# PLATINUM

collection

INTEGRATED LED

10 YEAR WARRANTY

## LED CHART

Lumens	1,600
Total Watts	16W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



DAMP

PCIN1616C

INTEGRATED LED

10 YEAR WARRANTY

## LED CHART

Lumens	1,800
Total Watts	18W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



DAMP

PCIN1613C

PLATINUM  
by QUOIZEL

# Infinity

FINISH: Polished Chrome

SHADE: Metal Rings with Crystals

INTEGRATED LED

10 YEAR WARRANTY

## LED CHART

Lumens	600
Total Watts	6W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

DAMP

PCIN1808C



INTEGRATED LED


10 YEAR WARRANTY

## LED CHART

Lumens	2,400
Total Watts	24W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

DAMP

PCIN1820C



# Infinity

collection

ITEM	DIMENSIONS	CANOPY	LIGHT SOURCE
PCIN1613C	4" H, 12.5" W, 12.5" Dp.	13.75"	See Chart for LED Information
PCIN1616C	4" H, 15.5" W, 15.5" Dp.	10.5"	See Chart for LED Information
PCIN1808C	8.5" H*, 7.5" W, 7.5" Dp.	1.5" x 5"	See Chart for LED Information
PCIN1820C	3" H, 20" W, 20" Dp.	1.75" x 6"	See Chart for LED Information



# Abode

**FINISH:** Polished Chrome

**SHADE:** Inner: Clear Organza Shade with Grey Trim  
Outer: Laser-cut Metal



 **PCAE1712C**

 **PCVY1714C**



# Verity

**FINISH:** Polished Chrome

**SHADE:** Inner: Chiffon  
Outer: Laser-cut Metal with Crystal Drops



 **PCLG1715BN**



 **PCLG2822BN**



# Legion

**FINISH:** Brushed Nickel

**SHADE:** Crystal Balls and Etched Glass Diffuser

ITEM	DIMENSIONS	CANOPY	BULBS
<b>PCAE1712C</b>	8.5" H, 12" W, 12" Dp.	1" x 4.75"	2-75W Med. Base or 18W CFL
<b>PCLG1715BN</b>	10.5" H, 16.5" W, 16.5" Dp.	1.5" x 5"	3-100W Med. Base or 23W CFL
<b>PCLG2822BN</b>	12" H*, 22" W, 22" Dp.	.5" x 4.5"	5-100W Med. Base or 23W CFL
<b>PCVY1714C</b>	12" H, 15" W, 15" Dp.	1" x 6"	3-100W Med. Base or 23W CFL

All rod-hung fixtures come with 10' of wire. \*Comes with (2) 6" and (2) 12" Rods.

DAMP

PCLM1612C



*hanging crystals*

## Luminous

FINISH: Polished Chrome

DAMP

PCLM1505C



INTEGRATED LED  
10 YEAR WARRANTY

### LED CHART

Lumens	500
Total Watts	5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	NO



DAMP

PCST1818C

## Starlet

FINISH: Polished Chrome

SHADE: Outer: Laser-cut Metal with Crystal Accents



DAMP

PCST1614C

INTEGRATED LED  
10 YEAR WARRANTY

### LED CHART

Lumens	2,200
Total Watts	22W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

INTEGRATED LED  
10 YEAR WARRANTY

### LED CHART

Lumens	1,760
Total Watts	17.6W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

### ITEM

### DIMENSIONS

### CANOPY

### BULBS/LIGHT SOURCE

<b>PCLM1505C</b>	13" H, 5" W, 5" Dp.	1.5" x 4.75"	See Chart for LED Information
<b>PCLM1612C</b>	8" H, 12" W, 12" Dp.	1" x 10.5"	4-40W Clear G9 Xenon (Supplied)
<b>PCST1614C</b>	5.5" H, 14" W, 14" Dp.	1.5" x 12"	See Chart for LED Information
<b>PCST1818C</b>	5.5" H, 18" W, 18" Dp.	2.75" x 5"	See Chart for LED Information

# Sylvan

**FINISH:** Polished Chrome  
**SHADE:** Inner: White Fabric  
Outer: Metal

Detail



**DAMP**

**PCRD1504C**



*inside: solid crystal  
with cutouts*

**INTEGRATED LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	450
Total Watts	4.5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

# Radiance

**FINISH:** Polished Chrome  
**GLASS:** Clear & Crystal Accents

**DAMP**

**PCRD1812C**

**INTEGRATED LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	1350
Total Watts	13.5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



**DAMP**

**PCSN2817C**



ITEM	DIMENSIONS	CANOPY	BULBS/LIGHT SOURCE
<b>PCRD1504C</b>	11" H, 3.5" W, 3.5" Dp.	1.5" x 5"	See Chart for LED Information
<b>PCRD1812C</b>	11" H, 12" W, 12" Dp.	1.75" x 9.75"	See Chart for LED Information
<b>PCSN2817C</b>	21" H*, 17" W, 17" Dp.	1" x 5.5"	4-40W Clear G9 Xenon (Supplied)

## Glow

**FINISH:** White Lustre

**GLASS:** Frosted Etched Acrylic



### LED CHART

Lumens	900
Total Watts	9W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES




**DAMP** **PCAW1612W**

*can be used as wall mounts*



**DAMP** **PCAW1611W**



**DAMP** **PCLT1611C**

## Lunette

**FINISH:** Polished Chrome

**GLASS:** Clear with Crystal Sand



### LED CHART

Lumens	1,200
Total Watts	14W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	NO



**DAMP** **PCLT1612C**

ITEM	DIMENSIONS	CANOPY	LIGHT SOURCE
<b>PCAW1611W</b>	2" H, 11" W, 11" Dp.	1.5" x 6.5"	See Chart for LED Information
<b>PCAW1612W</b>	2" H, 12" W, 12" Dp.	1.5" x 7"	See Chart for LED Information
<b>PCLT1611C</b>	2.5" H, 10.5" W, 10.5" Dp.	1" x 8"	See Chart for LED Information
<b>PCLT1612C</b>	2.5" H, 12" W, 12" Dp.	1" x 10"	See Chart for LED Information





# Baton

**FINISH:** Polished Chrome

**GLASS:** Opal Etched

**MOUNTS**

**DAMP**

**PCBT8520C**

**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	2,566
Total Watts	35W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



**DAMP**

**PCBT8526C**

**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	3,365
Total Watts	45W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



**DAMP**

**PCAS8505C**

**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	1,690
Total Watts	22W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

# PLATINUM

by QUOIZEL

# Axis

**FINISH:** Polished Chrome

**GLASS:** Opal Etched

**MOUNTS**

**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	3,460
Total Watts	42W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	2,561
Total Watts	32W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



**DAMP**

**PCAS8520C**



**DAMP**

**PCAS8525C**

ITEM	DIMENSIONS	BACKPLATE	HCW0	LIGHT SOURCE
PCAS8505C	13" H, 4.5" W, 3.5" Dp.	4.75" x 4.5"	2.5"	See Chart for LED Information
PCAS8520C	4.5" H, 19.5" W, 3.5" Dp.	4.75" x 4.5"	2.5"	See Chart for LED Information
PCAS8525C	4.5" H, 25" W, 3.5" Dp.	4.75" x 4.5"	2.5"	See Chart for LED Information
PCBT8520C	5" H, 19.5" W, 4" Dp.	4.75" x 6.75"	2.5"	See Chart for LED Information
PCBT8526C	5" H, 25.5" W, 4" Dp.	4.75" x 6.75"	2.5"	See Chart for LED Information

**INTEGRATED LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	1,400
Total Watts	14W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



**DAMP** ■ **PCFY8602C**

## Fantasy

**FINISH:** Polished Chrome  
**GLASS:** Bubble Crystal

**INTEGRATED LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	2,100
Total Watts	21W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



**DAMP** ■ **PCFY8603C**

**INTEGRATED LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	2,800
Total Watts	28W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



*light shines through top and bottom*

**DAMP** ■ **PCFY8604C**

**PLATINUM**  
by QUOIZEL

**INTEGRATED LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	841
Total Watts	8W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



**DAMP** ■ **PCPE8519C**

**MOUNTS**

## Promenade

**FINISH:** Polished Chrome  
**SHADE:** Acrylic

ITEM	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
<b>PCFY8602C</b>	6.5" H, 14.5" W, 3.5" Dp.	4.75" x 12.25"	-	See Chart for LED Information
<b>PCFY8603C</b>	6.5" H, 23" W, 3.5" Dp.	4.75" x 20.75"	-	See Chart for LED Information
<b>PCFY8604C</b>	6.5" H, 31.5" W, 3.5" Dp.	4.75" x 29.5"	-	See Chart for LED Information
<b>PCPE8519C</b>	4.5" H, 19" W, 3" Dp.	4.25" x 6.75"	2.5"	See Chart for LED Information

# Paragon

**FINISH:** Polished Chrome

**GLASS:** Crystal Starnds

**MOUNTS** 

**DAMP**

**PRN8610C**



**DAMP**

**EME8610C**

**PLATINUM**  
by QUOIZEL

# Evermore

**FINISH:** Polished Chrome

**GLASS:** Faceted Crystals

**INTEGRATED LED**  
10 YEAR WARRANTY



**DAMP**

**PCGA8519C**

**MOUNTS** 

### LED CHART

Lumens	1,200
Total Watts	12W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

# Gala

**FINISH:** Polished Chrome

**GLASS:** Rectangular Crystals

**INTEGRATED LED**  
10 YEAR WARRANTY



**DAMP**

**PCGA8524C**

### LED CHART

Lumens	1,800
Total Watts	18W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS/LIGHT SOURCE
<b>EME8610C</b>	5" H, 38.5" W, 7" Dp.	4.75" x 7"	2.5"	10-20W Clear G4 Xenon (Supplied)
<b>PCGA8519C</b>	5" H, 18.5" W, 5" Dp.	6.25" x 4.75"	3.5"	See Chart for LED Information
<b>PCGA8524C</b>	5" H, 24" W, 5.5" Dp.	6.25" x 4.75"	3.5"	See Chart for LED Information
<b>PRN8610C</b>	5" H, 36" W, 4" Dp.	4.75" x 7"	2.5"	10-20W Clear G4 Xenon (Supplied)

# Kyle

**FINISH:** Iron Gate

**SHADE:** White Onyx

*Also available in Imperial Bronze Finish with Butterscotch Onyx Shades.*

**DAMP** KY5503IN



**DAMP** KY5506IN



**NEW!**  
ADDITION

**DAMP** KY433IN



## Kyle collection

ITEM	DIMENSIONS	CANOPY	BULBS
KY433IN	18.5" H, 32.5" W, 4" Dp.	1.5" x 4.5"	4-100W Med. Base or 23W CFL
KY5503IN	19.5" H, 17" W, 17" Dp.	1" x 5.5"	3-100W Med. Base or 23W CFL
KY5506IN	23" H, 23" W, 23" Dp.	1" x 5.5"	6-100W Med. Base or 23W CFL



**DAMP** **RVN5303VG**



**Riverton**  
**FINISH:** VG - Vintage Gold  
 WT - Western Bronze

**DAMP** **RVN5303WT**



← hanging crystals

**Berwick**  
**FINISH:** Western Bronze

**DAMP** **BWK5204WT**



**Denton**  
**FINISH:** Western Bronze



**DAMP** **DTN5005WT**

ITEM	DIMENSIONS	CANOPY	BULBS
<b>BWK5204WT</b>	23" H, 14" W, 14" Dp.		4-60W Vintage Bulbs (Supplied)*
<b>DTN5005WT</b>	22.5" H, 28.5" W, 28.5" Dp.	1.5" x 6"	5-60W Vintage Bulbs (Supplied)*
<b>RVN5303VG</b>	21.5" H, 16" W, 16" Dp.	1.5" x 5"	3-60W Cand. Base
<b>RVN5303WT</b>	21.5" H, 16" W, 16" Dp.	1.5" x 5"	3-60W Cand. Base

Chain-hung fixtures come with 8' of wire & 4' of chain. \*MAX WATTAGE: 100W Med. Base or 23W CFL.

*Afton*

FINISH: Antique Nickel



DAMP ■ ATN5204AN

*Fort Quinn*

FINISH: Mercado Black



DAMP ■ FQ1913MK01

*Detail*



← *hanging optic crystal*

DAMP ■ BWS5303BN



DAMP ■ BWS5006BN

*Brightwaters*

FINISH: Brushed Nickel

ITEM	DIMENSIONS	CANOPY	BULBS
ATN5204AN	22" H, 16" W, 16" Dp.	1.5" x 6"	4-60W Cand. Base
BWS5006BN	33" H, 26" W, 26" Dp.	1.5" x 6"	6-60W Cand. Base
BWS5303BN	26.5" H, 18" W, 18" Dp.	1.5" x 6"	3-60W Cand. Base
FQ1913MK01	28" H, 18" W, 18" Dp.	1.5" x 6.5"	4-60W Cand. Base

## Cinema

**FINISH:** BN - Brushed Nickel  
WT - Western Bronze



*all tracks are flexible and the shades turn*


INTEGRATED **LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	2,600
Total Watts	35W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	YES

## Theater

**FINISH:** BN - Brushed Nickel  
WT - Western Bronze



ITEM	DIMENSIONS	CANOPY	LIGHT SOURCE
CMA1405BN	12" H, 5" W, 108" Dp.	1.5" x 4.75"	See Chart for LED Information
CMA1405WT	12" H, 5" W, 108" Dp.	1.5" x 4.75"	See Chart for LED Information
THR1405BN	11" H, 5" W, 108" Dp.	1.5" x 4.75'	See Chart for LED Information
THR1405WT	11" H, 5" W, 108" Dp.	1.5" x 4.75"	See Chart for LED Information

## Spiral

**FINISH:** Mystic Black

**SHADE:** Inner: White Fabric  
Outer: Metal

**DAMP** SPL1508K

Detail



Convertible to Semi-Flush



## Avondale

**FINISH:** Empire Brass

**SHADE:** Mica

QUOIZEL  
**NATURALS**  
**MICA**

**DAMP** SPL2820K

Convertible to Semi-Flush



**DAMP** ADE2822ER

ITEM	DIMENSIONS	CANOPY	BULBS
ADE2822ER	6.5" H*, 22" W, 22" Dp.	0.75" x 4.75"	4-60W Med. Base or 13W CFL
SPL1508K	10.5" H*, 8.5" W, 8.5" Dp.	1" x 5"	1-100W Med. Base or 23W CFL
SPL2820K	8" H*, 20" W, 20" Dp.	1" x 5.1"	3-100W Med. Base or 23W CFL



# Cambria

**FINISH:** Western Bronze


**GLASS:** Etched



**CBA5204WT**



**LND1510MC**



# Landings

**FINISH:** Mottled Cocoa

**SHADE:** Inner: Tan Fabric  
Outer: Metal Wire

*Convertible to Semi-Flush*



**LND2820MC**



ITEM	DIMENSIONS	CANOPY	BULBS
<b>CBA5204WT</b>	27.5" H*, 15.5" W, 15.5" Dp.	1.5" x 5"	4-100W Med. Base or 23W CFL
<b>LND1510MC</b>	9" H*, 10" W, 10" Dp.	1" x 6"	1-100W Med. Base or 23W CFL
<b>LND2820MC</b>	9" H*, 20" W, 20" Dp.	1" x 6"	4-100W Med. Base or 23W CFL

All rod-hung fixtures come with 10' of wire. \*Comes with (2) 6" and (2) 12" Rods.

## Boutique

**FINISH:** Mystic Black

**SHADE:** Inner: Oyster Mica  
Outer: Laser-cut Metal with Crystal Accents

*Convertible to Semi-Flush*



*Convertible to Semi-Flush*



*Detail*



**MCBQ2822K**



**MCBQ2818K**



**MC2443WT**

## Portal

**FINISH:** Western Bronze

**SHADE:** Oyster Mica & Tiffany Glass

QUOIZEL  
**NATURALS**  
**MICA**

*Convertible to Semi-Flush*



### ITEM

### DIMENSIONS

### CANOPY

### BULBS

**MC2443WT**

7" H\*, 18" W, 18" Dp.

1" x 6"

3-60W Med. Base or 13W CFL

**MCBQ2818K**

9" H\*, 18" W, 18" Dp.

0.75" x 6"

3-100W Med. Base or 23W CFL

**MCBQ2822K**

9" H\*, 22" W, 22" Dp.

1" x 6"

4-100W Med. Base or 23W CFL

# Boundary

**FINISH:** Polished Chrome

**SHADE:** Inner: Silver Organza  
Outer: Clear Mosaic Tile



**DAMP**

**BNY2816C**

**DAMP**

**BNY1506C**

*Detail*



**DAMP**

**BNY2822C**

*Convertible to Semi-Flush*



## ITEM

## DIMENSIONS

## CANOPY

## BULBS

**BNY1506C**

8.5" H\*, 6.5" W, 6.5" Dp.

0.75" x 5"

1-100W Med. Base or 23W CFL

**BNY2816C**

7" H\*, 16" W, 16" Dp.

0.75" x 5"

3-100W Med. Base or 23W CFL

**BNY2822C**

6.5" H\*, 22.5" W, 22.5" Dp.

0.75" x 5"

5-100W Med. Base or 23W CFL

All rod-hung fixtures come with 10' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# SEMI-FLUSH & FLUSH



**DAMP**

**MYS1616C**

**INTEGRATED LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	2,200
Total Watts	22W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

## Moon Rays

**FINISH:** Polished Chrome

**GLASS:** Cast Sandblasted Inside



**DAMP**

**MYS1612C**

**INTEGRATED LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	1,700
Total Watts	17W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

## Whitecap

**FINISH:** Mottled Cocoa

**GLASS:** Amber



**DAMP**

**WHP1712MC**

## Westchester

**FINISH:** Brushed Nickel

**GLASS:** Clear



**DAMP**

**WCR1613BN**



**DAMP**

**AX1716PN**

## Alexandria

**FINISH:** Palladian Bronze

*dangling glass accents*

ITEM	DIMENSIONS	CANOPY	BULBS/LIGHT SOURCE
<b>AX1716PN</b>	12" H, 16" W, 16" Dp.	0.75" x 5"	3-100W Med. Base or 23W CFL
<b>MYS1612C</b>	6" H, 12" W, 12" Dp.	1.75" x 8"	See Chart for LED Information
<b>MYS1616C</b>	6" H, 16" W, 16" Dp.	1.75" x 10"	See Chart for LED Information
<b>WCR1613BN</b>	9.5" H, 13" W, 13" Dp.	1.5" x 5.5"	3-60W Cand. Base
<b>WHP1712MC</b>	9" H, 12" W, 12" Dp.	1.5" x 5.5"	3-60W Cand. Base





## Landings

**FINISH:** Mottled Cocoa  
**SHADE:** Inner: Tan Fabric  
 Outer: Metal Wire

 **DAMP** ■ **LND1616MC**



## Boundary

**FINISH:** Polished Chrome  
**SHADE:** Inner: Silver Organza  
 Outer: Clear Mosaic Tile

 **DAMP** ■ **BNY1716C**



## Victory

**FINISH:** Valiant Bronze  
**SHADE:** Contains 216 Pieces of Tiffany Glass

 **DAMP** ■ **TFVY1400VA**

## Avondale

**FINISH:** Empire Brass  
**SHADE:** Mica



QUOIZEL  
**NATURALS**  
**MICA**



 **DAMP** ■ **ADE1716ER**

ITEM	DIMENSIONS	CANOPY	BULBS
<b>ADE1716ER</b>	10.5" H, 16" W, 16" Dp.	0.75" x 4.75"	3-60W Med. Base or 13W CFL
<b>BNY1716C</b>	12" H, 16.5" W, 16.5" Dp.	0.75" x 5"	3-100W Med. Base or 23W CFL
<b>LND1616MC</b>	9" H, 16" W, 16" Dp.	1" x 9.75"	3-100W Med. Base or 23W CFL
<b>TFVY1400VA</b>	5" H, 16.5" W, 16.5" Dp.	1.5" x 7.5"	2-60W Med. Base or 13W CFL



TF2600FVA

*Red Maple*



*Flowing Heart*

TF2582T




TF2600TVA



*Jungle Dragonfly*

TF2598T

ITEM	DIMENSIONS	BULBS	FINISH	GLASS
TF2582T	24.5" H, 15.5" W, 15.5" Dp.	2-75W Med. Base or 18W CFL	-	Contains 488 Pieces of Tiffany Glass
TF2598T	23.5" H, 17.5" W, 17.5" Dp.	2-75W Med. Base or 18W CFL	Architectural Bronze	Contains 552 Pieces of Tiffany Glass
TF2600FVA	61" H, 23.5" W, 23.5" Dp.	3-100W Med. Base or 23W CFL	Valiant Bronze	Contains 1086 Pieces of Tiffany Glass
TF2600TVA	33" H, 23.5" W, 23.5" Dp.	3-100W Med. Base or 23W CFL	Valiant Bronze	Contains 1086 Pieces of Tiffany Glass



TF2601FVB

Royal  
Briar



Cobalt

TF2599TVB



TF2601TVB



QUOIZEL  
NATURALS  
MICA

TF2591TIB

Persian  
Violet

ITEM	DIMENSIONS	BULBS	FINISH	GLASS
TF2591TIB	22" H, 14" W, 14" Dp.	2-60W Med. Base or 13W CFL	Imperial Bronze	Contains 200 Pieces of Tiffany & Mica Glass
TF2599TVB	27" H, 18.5" W, 18.5" Dp.	3-100W Med. Base or 23W CFL	Vintage Bronze	Contains 1099 Pieces of Tiffany Glass
TF2601FVB	61" H, 21" W, 21" Dp.	3-100W Med. Base or 23W CFL	Vintage Bronze	Contains 1252 Pieces of Tiffany Glass
TF2601TVB	28" H, 21" W, 21" Dp.	3-100W Med. Base or 23W CFL	Vintage Bronze	Contains 1252 Pieces of Tiffany Glass

Theory

SHADE: Multi-Colored Mica



MC2581T

QUOIZEL  
NATURALS  
MICA



Hideaway

FINISH: Western Bronze

SHADE: Inner: Oyster Mica  
Outer: Metal

Q2595TWT



Landings

FINISH: Mottled Cocoa

SHADE: Inner: Tan Fabric  
Outer: Metal Wire

LND6326MC

Spirit

SHADE: White Linen

Q2609T



Craft

SHADE: Tan Fabric

Q2613T

ITEM	DIMENSIONS	BULBS	SHADE DIMS
LND6326MC	25" H, 16" W, 16" Dp.	2-100W Med. Base or 23W CFL	(7" x 12") x (12" x 14") x 14"
MC2581T	25" H, 15" W, 15" Dp.	2-60W Med. Base or 13W CFL	7" x 15" x 15"
Q2595TWT	24" H, 16" W, 16" Dp.	2-60W Med. Base or 13W CFL	(6.5" x 14") x (14" x 14") x 14"
Q2609T	32" H, 18" W, 18" Dp.	1-150W Med. Base or 40W CFL	(10.5" x 17") x (17" x 18") x 18"
Q2613T	29.5" H, 16.5" W, 16.5" Dp.	1-100W Med. Base or 23W CFL	(11" x 15") x (15" x 16.5") x 16.5"



# Elliot

**SHADE:** Off-White Linen



**Q2612F**



**Q2612T**



*string that moves shade*

**Q2592TOZ**

# Chester

**FINISH:** Old Bronze

**SHADE:** White Linen



**Q2592FOZ**

ITEM	DIMENSIONS	BULBS	SHADE DIMS
<b>Q2592FOZ</b>	58" H, 19" W, 13" Dp.	1-75W Med. Base or 18W CFL	(7.5" x 9.5") x (9.5" x 13") x 13"
<b>Q2592TOZ</b>	24.5" H, 17.5" W, 11" Dp.	1-75W Med. Base or 18W CFL	(6" x 8.5") x (8.5" x 11") x 11"
<b>Q2612F</b>	63.5" H, 17" W, 17" Dp.	1-100W Med. Base or 23W CFL	(13" x 12") x (12" x 17") x 17"
<b>Q2612T</b>	32" H, 15" W, 15" Dp.	1-100W Med. Base or 23W CFL	(12" x 12") x (12" x 15") x 15"



*Maze*

**FINISH:** Brushed Nickel  
**SHADE:** Beige Linen Fabric

**Q2597TBN**



*Stride*

**SHADE:** Beige Linen Fabric

**Q2590T**



*Smockey Pearl*

**SHADE:** White Fabric

**Q2610T**



**Q2611T**

ITEM	DIMENSIONS	BULBS	SHADE DIMS
<b>Q2590T</b>	24" H, 17" W, 11" Dp.	1-150W Med. Base or 40W CFL	(9.5" x 17") x (11" x 17") x 11"
<b>Q2597TBN</b>	29" H, 16" W, 10" Dp.	1-150W Med. Base or 40W CFL	(10" x 16") x (10" x 16") x 10"
<b>Q2610T</b>	21" H, 11" W, 11" Dp.	1-100W Med. Base or 23W CFL	(8.5" x 11") x (11" x 11") x 11"
<b>Q2611T</b>	28.5" H, 13.5" W, 13.5" Dp.	1-100W Med. Base or 23W CFL	(10" x 13.5") x (13.5" x 13.5") x 13.5"



## Lakeshore

**FINISH:** Polished Nickel

**SHADE:** White Linen

**Q2589FPK**



*faceted crystals* →

## Arctic

**FINISH:** Brushed Nickel

**SHADE:** Beige Fabric

**Q2596TBN**

## Riverfront

**FINISH:** Polished Nickel

**SHADE:** White Linen

**Q2607FPK**



ITEM	DIMENSIONS	BULBS	SHADE DIMS
<b>Q2589FPK</b>	65" H, 16.5" W, 16.5" Dp.	1-150W Med. Base or 40W CFL	(11.5" x 15.5") x (15.5" x 16.5") x 16.5"
<b>Q2596TBN</b>	30" H, 17" W, 17" Dp.	1-150W Med. Base or 40W CFL	(10" x 15") x (15" x 17") x 17"
<b>Q2607FPK</b>	65.5" H, 20" W, 20" Dp.	1-150W Med. Base or 40W CFL	(12" x 18") x (18" x 20") x 20"



## Stargaze

**SHADE:** Black Metal Mesh

**Q2606F**



## Overlook

**FINISH:** Oil Rubbed Bronze

**SHADE:** White Linen Fabric

**Q2605FOI**

ITEM	DIMENSIONS	BULBS	SHADE DIMS
<b>Q2605FOI</b>	90.5" H, 40" W, 38" Dp.	3-60W Med. Base or 13W CFL	(10" x 9") x (9" x 9") x 9"
<b>Q2606F</b>	93" H, 40" W, 38" Dp.	3-60W Vintage Bulbs (Supplied)*	-





**CFT9364BN**

**CFT9364OI**

**CFT6330BN**

## Clift

**FINISH:** BN - Brushed Nickel  
OI - Oil Rubbed Bronze

**SHADE:** BN - White Linen  
OI - White Linen

**CFT6330OI**

ITEM	DIMENSIONS	BULBS	SHADE DIMS
<b>CFT6330BN</b>	31.5" H, 12" W, 39" Dp.	1-75W Med. Base or 18W CFL	(8.5" x 11") x (11" x 11.5") x 11.5"
<b>CFT6330OI</b>	31.5" H, 12" W, 39" Dp.	1-75W Med. Base or 18W CFL	(8.5" x 11") x (11" x 11.5") x 11.5"
<b>CFT9364BN</b>	65" H, 12.5" W, 41" Dp.	1-75W Med. Base or 18W CFL	(8.5" x 12") x (12" x 12.5") x 12.5"
<b>CFT9364OI</b>	65" H, 12.5" W, 41" Dp.	1-75W Med. Base or 18W CFL	(8.5" x 12") x (12" x 12.5") x 12.5"

# Millington

**FINISH:** OI - Oil Rubbed Bronze  
PA - Polished Antique Nickel

**SHADE:** Off White Linen

VVMN9558PA



VVMN9558OI




VVMN9258OI



VVMN9258PA



ITEM	DIMENSIONS	BULBS	SHADE DIMS
VVMN9258OI	58.5" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL + 1-150W Med. Base or 40W CFL	(10" x 12") x (12" x 15") x 15"
VVMN9258PA	58.5" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL + 1-150W Med. Base or 40W CFL	(10" x 12") x (12" x 15") x 15"
VVMN9558OI	58" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL	(10" x 12") x (12" x 15") x 15"
VVMN9558PA	58" H, 15" W, 15" Dp.	3-75W Med. Base or 18W CFL	(10" x 12") x (12" x 15") x 15"




*Yane*  
**FINISH:** Brushed Nickel  
**SHADE:** Metal

**Q2603FBN**



**LED CHART**

Lumens	1,350
Total Watts	12W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO



*Bridge*  
**FINISH:** Brushed Nickel  
**SHADE:** Metal

**Q2604FBN**



**LED CHART**

	TOP	BOTTOM
Lumens	1,800	400
Total Watts	13W	3W
Color Rendering Index (CRI)	80	80
Color Temperature (CCT)	3000K	3000K
Dimmable	NO	YES



*Alfred*

**SHADE:** Metal

**Q2587T**



*Bradford*

**FINISH:** Polished Nickel  
**SHADE:** Metal

**Q2588TPK**

**ITEM**

**DIMENSIONS**

**BULBS/LIGHT SOURCE**

<b>Q2587T</b>	23" H, 18" W, 8.5" Dp.	1-75W Med. Base or 18W CFL
<b>Q2588TPK</b>	27" H, 17" W, 8" Dp.	1-75W Med. Base or 18W CFL
<b>Q2603FBN</b>	55" H, 13" W, 9" Dp.	See Chart for LED Information
<b>Q2604FBN</b>	70.5" H, 8.5" W, 8.5" Dp.	See Chart for LED Information



## Yenton

**FINISH:** Polished Nickel

**SHADE:** Metal

**Q2608FPK**



## Incline

**Q2602T**

INTEGRATED **LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	540
Total Watts	6W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	YES



## Crossway

**Q2593T**

*collapses close* →

## Edge

**Q2594T**

INTEGRATED **LED**  
10 YEAR WARRANTY

### LED CHART

Lumens	900
Total Watts	10W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	YES

**ITEM**

**DIMENSIONS**

**BULBS/LIGHT SOURCE**

<b>Q2593T</b>	17.5" H, 17.5" W, 2" Dp.	See Chart for LED Information
<b>Q2594T</b>	20.5" H, 7" W, 7" Dp.	See Chart for LED Information
<b>Q2602T</b>	18.5" H, 17.5" W, 4" Dp.	See Chart for LED Information
<b>Q2608FPK</b>	58" H, 18" W, 20" Dp.	1-75W Med. Base or 18W CFL



## Weave

**FINISH:** Brushed Nickel

**GLASS:** Clear

**MOUNTS**

G9 LED Bulb



Detail



DAMP

**WVE8602BNLED**



DAMP

**WVE8604BNLED**



DAMP

**WVE8603BNLED**

## Weave collection

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
<b>WVE8602BNLED</b>	5.5" H, 14" W, 5.5" Dp.	4.5" x 7"	3.5"	2-4.5W Frosted G9 LED Dimmable (Supplied)
<b>WVE8603BNLED</b>	5.5" H, 22" W, 5.5" Dp.	4.5" x 7"	3.5"	3-4.5W Frosted G9 LED Dimmable (Supplied)
<b>WVE8604BNLED</b>	5.5" H, 30.5" W, 5.5" Dp.	4.5" x 7"	3.5"	4-4.5W Frosted G9 LED Dimmable (Supplied)

Weave bath fixtures can be mounted as uplights or downlights.

## Kolt

**FINISH:** Brushed Nickel

**GLASS:** Inner: Heavy Sandblast  
Outer: Clear



**DAMP** KLT8602BNLED



**DAMP** KLT8603BNLED

**MOUNTS**



**DAMP** KLT8604BNLED



**DAMP** KLT8605BNLED

## Kolt collection

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
<b>KLT8602BNLED</b>	6" H, 13" W, 6.5" Dp.	6" x 6.5"	3.5"	2-4.5W Frosted G9 LED Dimmable (Supplied)
<b>KLT8603BNLED</b>	6" H, 21" W, 6.5" Dp.	6" x 6.5"	2.5"	3-4.5W Frosted G9 LED Dimmable (Supplied)
<b>KLT8604BNLED</b>	6" H, 29" W, 6.5" Dp.	6" x 6.5"	2.5"	4-4.5W Frosted G9 LED Dimmable (Supplied)
<b>KLT8605BNLED</b>	6" H, 42" W, 6.5" Dp.	5" x 18"	3.5"	5-4.5W Frosted G9 LED Dimmable (Supplied)

# Kolt

**FINISH:** Polished Chrome

**GLASS:** Inner: Heavy Sandblast  
Outer: Clear



**DAMP**

**KLT8605CLED**



**DAMP**

**BNN8602BNLED**

# Banner

**FINISH:** Brushed Nickel

**GLASS:** Etched Painted White Inside



**DAMP**

**BNN8603BNLED**



**DAMP**

**BNN8604BNLED**

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
<b>BNN8602BNLED</b>	5" H, 16" W, 4" Dp.	5" x 16"	2.5"	2-4.5W Frosted G9 LED Dimmable (Supplied)
<b>BNN8603BNLED</b>	5" H, 24" W, 4" Dp.	5" x 24"	2.5"	3-4.5W Frosted G9 LED Dimmable (Supplied)
<b>BNN8604BNLED</b>	5" H, 32" W, 4" Dp.	5" x 32"	2.5"	4-4.5W Frosted G9 LED Dimmable (Supplied)
<b>KLT8605CLED</b>	6" H, 42" W, 6.5" Dp.	5" x 18"	3.5"	5-4.5W Frosted G9 LED Dimmable (Supplied)



**DAMP** [ARC8603CLED](#)

## MOUNTS

### Arch

**FINISH:** Polished Chrome

**GLASS:** Opal Etched



**DAMP** [ARC8602CLED](#)



G9 LED Bulb



**DAMP** [ARC8604CLED](#)

## Arch collection

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
<b>ARC8602CLED</b>	7" H, 16.5" W, 5.5" Dp.	4.5" x 11"	4.5"	2-4.5W Frosted G9 LED Dimmable (Supplied)
<b>ARC8603CLED</b>	7" H, 25.5" W, 5.5" Dp.	4.5" x 11"	4.5"	3-4.5W Frosted G9 LED Dimmable (Supplied)
<b>ARC8604CLED</b>	7" H, 34.5" W, 5.5" Dp.	4.5" x 11"	4.5"	4-4.5W Frosted G9 LED Dimmable (Supplied)



# Trilogy

**FINISH:** BN - Brushed Nickel  
OZ - Old Bronze

**SHADE:** Clear Seedy

**DAMP**

**TRG8602BN**



**DAMP**

**TRG8603BN**



**DAMP**

**TRG8604BN**



**MOUNTS**

**DAMP**

**TRG8602OZ**



VINTAGE STYLE  
bulb included



**DAMP**

**TRG8603OZ**



**DAMP**

**TRG8604OZ**



## Trilogy collection

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
TRG8602BN/OZ	8.5" H, 17.5" W, 9" Dp.	4.5" x 8"	4.25"	2-60W Vintage Bulb (Supplied)*
TRG8603BN/OZ	8.5" H, 26.5" W, 9" Dp.	4.5" x 8"	4.25"	3-60W Vintage Bulb (Supplied)*
TRG8604BN/OZ	8.5" H, 36.5" W, 9" Dp.	4.5" x 8"	4.25"	4-60W Vintage Bulb (Supplied)*

Trilogy bath fixtures can be mounted as uplights or downlights. \*MAX WATTAGE: 100W Med. Base or 23W CFL.



**DAMP** ■ **ANW8603AN**

## Andrews

**FINISH:** Antique Nickel

**GLASS:** Clear

VINTAGE STYLE  
bulb included



**MOUNTS**



**DAMP** ■ **ANW8602AN**



**DAMP** ■ **ANW8604AN**

## Andrews collection

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
<b>ANW8602AN</b>	9" H, 14" W, 7" Dp.	6" x 6"	3.25"	2-60W Vintage Bulb (Supplied)*
<b>ANW8603AN</b>	9" H, 22" W, 7" Dp.	6" x 6"	3.25"	3-60W Vintage Bulb (Supplied)*
<b>ANW8604AN</b>	9" H, 30.5" W, 7" Dp.	6" x 6"	3.25"	4-60W Vintage Bulb (Supplied)*

# Highfield

**FINISH:** Brushed Nickel

**GLASS:** Opal Etched

**MOUNTS**

**DAMP** **HFD8602BN**



**DAMP** **HFD8604BN**



**DAMP** **HFD8603BN**

## Highfield collection

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
HFD8602BN	8" H, 14.5" W, 7" Dp.	4.5" x 6.5"	3.25"	2-100W Med. Base or 23W CFL
HFD8603BN	8" H, 22.5" W, 7" Dp.	4.5" x 6.5"	3.25"	3-100W Med. Base or 23W CFL
HFD8604BN	8" H, 30.5" W, 7" Dp.	4.5" x 6.5"	3.25"	4-100W Med. Base or 23W CFL

Highfield bath fixtures can be mounted as uplights or downlights.

## Taylor

**FINISH:** AN - Antique Nickel  
 BN - Brushed Nickel  
 C - Polished Chrome  
 WT - Western Bronze

**SHADE:** Opal Etched



## Taylor collection

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
TY8605AN	7.5" H, 40.5" W, 6" Dp.	4.5" x 11.5"	6.5"	5-100W Med. Base or 23W CFL
TY8605BN	7.5" H, 40.5" W, 6" Dp.	4.5" x 11.5"	6.5"	5-100W Med. Base or 23W CFL
TY8605C	7.5" H, 40.5" W, 6" Dp.	4.5" x 11.5"	6.5"	5-100W Med. Base or 23W CFL
TY8605WT	7.5" H, 40.5" W, 6" Dp.	4.5" x 11.5"	6.5"	5-100W Med. Base or 23W CFL





**DAMP** ■ **NL8605C**

# Nicholas

**FINISH:** BN - Brushed Nickel  
 C - Polished Chrome  
 HO - Harbor Bronze

**SHADE:** Opal Etched



**DAMP** ■ **NL8605HO**



**DAMP** ■ **NL8605BN**

## Nicholas collection

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
NL8605BN	11" H, 42" W, 7" Dp.	4.5" x 14"	6"	5-100W Med. Base or 23W CFL
NL8605C	11" H, 42" W, 7" Dp.	4.5" x 14"	6"	5-100W Med. Base or 23W CFL
NL8605HO	11" H, 42" W, 7" Dp.	4.5" x 14"	6"	5-100W Med. Base or 23W CFL

Nicholas bath fixtures can be mounted as uplights or downlights.

*Beacon*

**FINISH:** Stone Black

**GLASS:** Clear Seedy



Front View



**BEC8409SBK**



**BEC1909SBK**

**BEC8409SBK**

**BEC9009SBK**

**LED CHART**

Lumens	1,650
Total Watts	22W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO



**WET** ■ **BEC8406SBK**

**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	980
Total Watts	14W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO

**WET** ■ **BEC1909SBK**

**Indoor  
Outdoor**



**WET** ■ **BEC9009SBK**

**WINNER**  
*Market Choice  
Award*



**WET** ■ **BEC8408SBK**

**INTEGRATED LED**  
10 YEAR WARRANTY

**LED CHART**

Lumens	1,300
Total Watts	18W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO

# Beacon collection

ITEM	DIMENSIONS	BACKPLATE	HCW0	LIGHT SOURCE
BEC1909SBK	17" H*, 9" W, 8" Dp.	1" x 5.25"	-	See Chart for LED Information
BEC8406SBK	13" H, 6" W, 6.5" Dp.	4.5" x 4.5"	5"	See Chart for LED Information
BEC8408SBK	15" H, 7.5" W, 7.5" Dp.	5.25" x 5.5"	5.75"	See Chart for LED Information
BEC8409SBK	17" H, 9" W, 9" Dp.	6.25" x 6.25"	6.25"	See Chart for LED Information
BEC9009SBK	19" H, 9" W, 8" Dp.	-	-	See Chart for LED Information

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

# Livingston

**FINISH:** Imperial Bronze

**GLASS:** Clear Seedy



by QUOIZEL

5-Year Warranty



Front View



LVN8408IB



LVN1908IB

LVN8408IB

LVN9008IB

**LED CHART**

Lumens	1,650
Total Watts	22W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO



Indoor  
Outdoor

WET LVN1908IB



WET LVN8406IB

INTEGRATED LED  
10 YEAR WARRANTY

LED CHART

Lumens	720
Total Watts	10W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO

WET LVN9008IB



WET LVN8407IB

INTEGRATED LED  
10 YEAR WARRANTY

LED CHART

Lumens	1,300
Total Watts	18W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO



# Livingston collection

ITEM	DIMENSIONS	BACKPLATE	HCWO	LIGHT SOURCE
LVN1908IB	18.5" H*, 8.5" W, 6.5" Dp.	1" x 5"	-	See Chart for LED Information
LVN8406IB	11" H, 6" W, 5.5" Dp.	6.5" x 3.75"	3.5"	See Chart for LED Information
LVN8407IB	13.5" H, 7.5" W, 7" Dp.	7.5" x 4.75"	3.75"	See Chart for LED Information
LVN8408IB	16.5" H, 8.5" W, 8" Dp.	9.25" x 6"	5.25"	See Chart for LED Information
LVN9008IB	19.5" H, 8.5" W, 5" Dp.	-	-	See Chart for LED Information

Outdoor hanging fixtures come with 12' of wire and 8' of chain.

## Stonington

**FINISH:** K - Matte Black  
 PN - Palladian Bronze  
 W - Fresco

**GLASS:** Clear Water



To order **Title 24 Compliant** outdoor fixtures, please add "FL" to the end of any style number displaying the Title 24 logo (Medium Base bulbs only). CFL Bulbs Supplied.



by QUOIZEL

5-Year Warranty



CFL Bulbs Not Shown



**SNN8411K**



**SNN8411W**



**SNN8411PN**



**SNNL8411PN**



**SNNL8411K**  
**SNNL8411PN**

### LED CHART

Lumens	1,350
Total Watts	22W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO



**SNNL8411K**

## Stonington collection

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS/LIGHT SOURCE
<b>SNN8411K</b>	17" H, 11" W, 12" Dp.	8" x 4.75"	3.5"	1-150W Med. Base or 40W CFL
<b>SNN8411PN</b>	17" H, 11" W, 12" Dp.	8" x 4.75"	3.5"	1-150W Med. Base or 40W CFL
<b>SNN8411W</b>	17" H, 11" W, 12" Dp.	8" x 4.75"	3.5"	1-150W Med. Base or 40W CFL
<b>SNNL8411K</b>	17" H, 11" W, 12" Dp.	8" x 4.75"	3.5"	See Chart for LED Information
<b>SNNL8411PN</b>	17" H, 11" W, 12" Dp.	8" x 4.75"	3.5"	See Chart for LED Information

**WET** MBU8407WT



**STAINLESS Steel**

**WET** MBU8407SS

INTEGRATED **LED**  
10 YEAR WARRANTY

**MBU8407SS**  
**MBU8407WT**  
**MBU8408SS**  
**MBU8408WT**

**LED CHART**

Lumens	800
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3000K
Dimmable	NO

*Malibu*

**FINISH:** SS - Stainless Steel  
WT - Western Bronze

**GLASS:** Opal Etched



**STAINLESS Steel**

**WET** MBU8408SS



**WET** MBU8408WT

*Malibu* collection

ITEM	DIMENSIONS	BACKPLATE	HCW0	LIGHT SOURCE
<b>MBU8407SS</b>	13" H, 6" W, 7" Dp.	7" x 4.75"	3.5"	See Chart for LED Information
<b>MBU8407WT</b>	13" H, 6" W, 7" Dp.	7" x 4.75"	3.5"	See Chart for LED Information
<b>MBU8408SS</b>	16" H, 7.5" W, 8.5" Dp.	8.5" x 4.75"	4.5"	See Chart for LED Information
<b>MBU8408WT</b>	16" H, 7.5" W, 8.5" Dp.	8.5" x 4.75"	4.5"	See Chart for LED Information

ADE1716ER.....	33	CFT9364BN .....	41	MC2581T.....	36
ADE2822ER.....	28	CFT9364OI .....	41	MCBQ2818K .....	30
ANW8602AN .....	50	CMA1405BN .....	27	MCBQ2822K .....	30
ANW8603AN .....	50	CMA1405WT .....	27	MYS1612C.....	32
ANW8604AN .....	50	DTN5005WT.....	25	MYS1616C.....	32
ARC8602CLED .....	48	EME8610C .....	23	NL8605BN.....	53
ARC8603CLED .....	48	FQ1913MK01.....	26	NL8605C .....	53
ARC8604CLED .....	48	HFD8602BN .....	51	NL8605HO .....	53
ATN5204AN .....	26	HFD8603BN .....	51	PCAE1712C.....	17
AX1716PN .....	32	HFD8604BN .....	51	PCAS8505C .....	21
BEC1909SBK .....	55	KLT8602BNLED .....	46	PCAS8520C .....	21
BEC8406SBK .....	55	KLT8603BNLED .....	46	PCAS8525C .....	21
BEC8408SBK .....	55	KLT8604BNLED .....	46	PCAW1611W.....	20
BEC8409SBK .....	54	KLT8605BNLED .....	46	PCAW1612W.....	20
BEC9009SBK .....	55	KLT8605CLED.....	47	PCBT8520C .....	21
BGD1716WT.....	9	KY433IN.....	24	PCBT8526C .....	21
BGD2820WT.....	9	KY5503IN .....	24	PCBZ1612C .....	14
BGD5006WT.....	8	KY5506IN .....	24	PCBZ1616C .....	14
BGD5203WT.....	9	LND1510MC.....	29	PCCC1614C.....	14
BNN8602BNLED .....	47	LND1616MC.....	33	PCCC1814C.....	14
BNN8603BNLED .....	47	LND2820MC.....	29	PCCN2818PK .....	13
BNN8604BNLED .....	47	LND6326MC.....	36	PCCN2824PK .....	13
BNY1506C.....	31	LVN1908IB .....	57	PCER1718C .....	13
BNY1716C.....	33	LVN8406IB .....	57	PCFY8602C .....	22
BNY2816C.....	31	LVN8407IB .....	57	PCFY8603C .....	22
BNY2822C.....	31	LVN8408IB .....	56	PCFY8604C .....	22
BWK5204WT .....	25	LVN9008IB .....	57	PCGA8519C .....	23
BWS5006BN.....	26	MBU8407SS .....	59	PCGA8524C .....	23
BWS5303BN.....	26	MBU8407WT .....	59	PCGO1616C .....	15
CBA5204WT .....	29	MBU8408SS .....	59	PCGO1816C .....	15
CFT6330BN .....	41	MBU8408WT .....	59	PCGO1822C .....	15
CFT6330OI .....	41	MC2443WT .....	30	PCIN1613C.....	16



PCIN1616C.....	16	Q2605FOI.....	40	TRG1716BN.....	11
PCIN1808C.....	16	Q2606F .....	40	TRG1816BN.....	11
PCIN1820C.....	16	Q2607FPK.....	39	TRG5103BN.....	11
PCLG1715BN .....	17	Q2608FPK.....	44	TRG5105BN.....	10
PCLG2822BN .....	17	Q2609T .....	36	TRG8602BN .....	12, 49
PCLM1505C .....	18	Q2610T .....	38	TRG8602OZ .....	12, 49
PCLM1612C .....	18	Q2611T .....	38	TRG8603BN .....	12, 49
PCLT1611C .....	20	Q2612F .....	37	TRG8603OZ .....	12, 49
PCLT1612C .....	20	Q2612T .....	37	TRG8604BN .....	12, 49
PCPE8519C .....	22	Q2613T .....	36	TRG8604OZ .....	12, 49
PCPI1815C .....	15	RVN5303VG .....	25	TRG8701BN.....	10
PCRD1504C.....	19	RVN5303WT.....	25	TY8605AN.....	52
PCRD1812C.....	19	SNN8411K .....	58	TY8605BN .....	52
PCSN2817C.....	19	SNN8411PN .....	58	TY8605C.....	52
PCST1614C.....	18	SNN8411W .....	58	TY8605WT .....	52
PCST1818C.....	18	SNNL8411K.....	58	VVMN9258OI.....	42
PCVY1714C .....	17	SNNL8411PN .....	58	VVMN9258PA .....	42
PRN8610C.....	23	SPL1508K.....	28	VVMN9558OI.....	42
Q2587T .....	43	SPL2820K.....	28	VVMN9558PA .....	42
Q2588TPK.....	43	TF2582T .....	34	WCR1613BN .....	32
Q2589FPK.....	39	TF2591TIB .....	35	WHP1712MC.....	32
Q2590T .....	38	TF2598T .....	34	WVE8602BNLED .....	45
Q2592FOZ .....	37	TF2599TVB.....	35	WVE8603BNLED .....	45
Q2592TOZ .....	37	TF2600FVA.....	34	WVE8604BNLED .....	45
Q2593T .....	44	TF2600TVA.....	34		
Q2594T .....	44	TF2601FVB.....	35		
Q2595TWT .....	36	TF2601TVB.....	35		
Q2596TBN .....	39	TFVY1400VA .....	33		
Q2597TBN .....	38	THR1405BN.....	27		
Q2602T .....	44	THR1405WT .....	27		
Q2603FBN .....	43	TRG1508BN.....	11		
Q2604FBN .....	43	TRG1712BN.....	11		

[www.QUOIZEL.com](http://www.QUOIZEL.com)

### **Corporate Headquarters**

6 Corporate Parkway, Goose Creek, SC 29445  
Phone: (843) 553-6700

### **Corporate Headquarters/ Customer Service**

590 Old Willets Path, Hauppauge, NY 11788  
Phone: (631) 273-2700  
Fax: (631) 231-7102  
Toll-Free Consumer Hotline: (800) 645-3184

### **Showroom - Dallas Trade Mart**

3rd Floor, Space 3200, Dallas, TX 75207  
Phone: (214) 747-3665

### **Showroom - High Point Market**

Showplace 3515  
211 E. Commerce Ave., High Point, NC 27260



**CQ2616X**

© Quozel, Inc.