



Contemporary Lighting™

COLLECTIONS

Alumilux | 123

Apex | 109

Apollo | 31

Arhaus | 115

Aura | 1

Blade | 59

Caps | 118

Cells | 27

Chaos | 65

Cilandro LED | 117

Cirque | 17

Concentric | 53

Cyborg | 51

Dazed | 5

Donuts | 55

Fizz III | 81

Gem | 119

Hilite | 91

Hoops | 33

Inca | 121

Kriss Kross | 9

Palette | 43

Pandora | 57

Parasol | 99

Polka | 95

Puffs | 69

Quad | 23

Quantum | 63

Rhombus | 61

Roller | 13

Rondelle | 118

Saturn | 15

Scepter | 75

Sense II | 105

Solar | 111

Solitaire | 87

Stage | 113

Timbale | 39

Volt | 47

MORE

Finishes | 137

Glass | 137

Index | 135

Lamping Guide | 138

Replacement Bulbs | 139

Shades | 137

Warranty | 140

LEGEND



ADA
Compliant



Driver
Power Source



Installs
Up or Down



Adjustable



Low-Voltage
Electronic
Dimmer



Slope



Ballast
Power Source



Energy
Efficient



Transformer
Power Source



Dimmable using standard dimmer.
Lutron® CL dimmers are recommended.

HCO | Height from Center of Outlet
OAH | Overall Height




AURA

A sculpture of Polished Chrome channel is gracefully formed with offsetting waves of motion. This collection is fully dimmable for a great combination of form and function.

AURA

- Functional sculptures of illumination
- Fully dimmable high-powered LEDs
- Diodes visible to create contemporary look
- 3000K Color Temperature
- CRI-80



E21178-PC
18-Light Pendant
Finish: Polished Chrome
149W LED (Lamps Included)
10,433 Lumens
38" / 158" OAH




AURA

- Functional sculptures of illumination
- Fully dimmable high-powered LEDs
- Diodes visible to create contemporary look
- 3000K Color Temperature
- CRI-80




E21176-PC

16-Light Pendant
Finish: Polished Chrome
103.7W LED (Lamps Included)
7,258 Lumens
28" / 148" OAH




AURA



E21174-PC
14-Light Pendant
Finish: Polished Chrome
60.5W LED (Lamps Included)
4,234 Lumens
22" / 142" OAH



E21172-PC
10-Light Pendant
Finish: Polished Chrome
32.4W LED (Lamps Included)
2,268 Lumens
18" / 134" OAH





DAZED


Sculptures created from Polished Chrome aluminum rods are formed by hand into a mod-silhouette, perfect for loft living and cosmopolitan lifestyles. Woven through the interior are strings of clear G4 Xenon lamps that add sparkle as they reflect off of the embellished etched patterns of the aluminum. Fashion forward and style genre-defying, the Dazed collection goes with a myriad of looks from art deco to pop art.

DAZED

- Clear string of G4, Xenon Lamps
- State-of-the-art Smith & Kole 12V transformers
- High Polished Chrome Aluminum rods
- Hand formed Mod-Silhouettes
- Dimmable




E22576-PC
15-Light Pendant
Finish: Polished Chrome
15 x 20W G4 (Lamps Included)
3,900 Lumens
36" / 154.75" OAH



DAZED




E22578-PC
12-Light Pendant
Finish: Polished Chrome
12 x 20W G4 (Lamps Included)
3,120 Lumens
24.5" / 133.75" OAH



• Strings of clear G4 Xenon lamps woven through the Interior

DAZED

- Clear string of G4, Xenon Lamps
- State-of-the-art Smith & Kole 12V transformers
- High Polished Chrome Aluminum rods
- Hand formed Mod-Silhouettes
- Dimmable



E22572-PC
8-Light Pendant
Finish: Polished Chrome
8 x 20W G4 (Lamps Included)
2,080 Lumens
24" / 142" OAH



E22574-PC
12-Light Pendant
Finish: Polished Chrome
12 x 20W G4 (Lamps Included)
3,120 Lumens
28.5" / 147" OAH





KRISS KROSS

Micro channels of Polished Chrome aluminum are faced with an acrylic diffuser and are arranged in a crisscross formation to create an interesting sculpture of light. Although pre-set out of the box, each are adjustable so to create your own unique design.

KRISS KROSS


- Thin strips of LED are housed in channels of Polished Chrome Aluminum
- Arranged in a crisscross formation to create functional sculptures of light
- Adjustable to create your own design
- 3000K Color Temperature
- CRI 80



E20697-PC

16-Light Pendant
Finish: Polished Chrome
91.2W LED (Lamps Included)
6,384 Lumens
52.25" / 84.5" OAH


- Includes One 6" stem ESTR06206PC
- Includes Three 12" stems ESTR06212PC



KRISS KROSS



LED



E20695-PC
8-Light Pendant
Finish: Polished Chrome
45.6W LED (Lamps Included)
3,192 Lumens
31" / 72.75" OAH

- Includes One 6" stem **ESTR06206PC**
- Includes Three 12" stems **ESTR06212PC**




KRISS KROSS


- Thin strips of LED are housed in channels of Polished Chrome Aluminum
- Arranged in a crisscross formation to create functional sculptures of light
- Adjustable to create your own design
- 3000K Color Temperature
- CRI 80



E20693-PC
6-Light Flush Mount
Finish: Polished Chrome
34.2W LED (Lamps Included)
2,394 Lumens





E20691-PC
3-Light Wall Mount
Finish: Polished Chrome
17.1W LED (Lamps Included)
1,197 Lumens
HCO: 13"



ROLLER

Dual pieces of Matte White aluminum gently wave in tandem to create a unique contemporary form. With powerful COB LEDs mounted on top and bottom, you receive ample down light and an indirect up light that creates a dramatic effect in the room.



E22824-MW
7-Light Pendant
Finish: Matte White
35W COB LED (Lamps Included)
2,450 Lumens
4.75" / 121" OAH



• Uplight



• Downlight




ROLLER

- Gentle waves of aluminum in Matte White finish
- High-powered integrated LED modules
- 3000K Color Temperature
- Designed to give ample down light and ambient up light



E22822-MW
 5-Light Pendant
 Finish: Matte White
 25W COB LED (Lamps Included)
 1,750 Lumens
 4.75" / 121" OAH



E22820-MW
 4-Light Wall Mount
 Finish: Matte White
 20W COB LED (Lamps Included)
 1,400 Lumens
 HCO: 7.25"






SATURN


The Saturn truly lives up to its name with rings of Metallic Silver or Bronze cast metal supporting bands of Frost acrylic. The LED lights add an out of this world touch with illumination that can be controlled with a standard wall dimmer.

SATURN


- 3000K Color Temperature
- Two finish options available, Metallic Silver or Bronze
- Lutron® CL™ Dimmers are recommended
- Adjusts to Multiple configuration




E22455-11BZ
E22455-11MS
 LED Pendant
 Finish: See Images
 Glass: Frost Acrylic
 40W LED (Lamps Included)
 2,800 Lumens
 35.75" / 51.5" OAH



E22456-11MS
E22456-11BZ
 LED Pendant
 Finish: See Images
 Glass: Frost Acrylic
 70W LED (Lamps Included)
 4,900 Lumens
 35.75" / 109" OAH



E22453-11MS
E22453-11BZ
 LED Pendant
 Finish: See Images
 Glass: Frost Acrylic
 24W LED (Lamps Included)
 1,680 Lumens
 35.75" / 51.5" OAH




CIRQUE

Matte White rings suspend in a unique fashion as if relying on each other for support. A continuous band of LED evenly spread generous amounts of dimmable light into the space. Ceiling fixtures can also double as wall mounts.

CIRQUE


- High-powered LED rings that fit into each other
- Ceiling Mounts also function as Wall Sconces
- 3000K Color Temperature
- CRI >80



E22849-MW
LED Pendant
Finish: Matte White
Glass: Acrylic
195W LED (Lamps Included)
10,025 Lumens
20" / 134" OAH



CIRQUE




E22848-MW
LED Pendant
Finish: Matte White
Glass: Acrylic
100W LED (Lamps Included)
6,150 Lumens
16" / 129" OAH



- High-powered LED rings that fit into each other
- Ceiling Mounts also function as Wall Sconces
- 3000K Color Temperature
- CRI >80

CIRQUE





E22847-MW
 LED Pendant
 Finish: Matte White
 Glass: Acrylic
 67W LED (Lamps Included)
 4,690 Lumens
 13" / 126" OAH



CIRQUE

- High-powered LED rings that fit into each other
- Ceiling Mounts also function as Wall Sconces
- 3000K Color Temperature
- CRI >80




E22845-MW
LED Pendant
Finish: Matte White
Glass: Acrylic
51W LED (Lamps Included)
3,570 Lumens
12" / 121" OAH



CIRQUE




• Wall Mount Option



E22840-MW
LED Flush/Wall Mount
Finish: Matte White
Glass: Acrylic
20W LED (Lamps Included)
1,400 Lumens




• Wall Mount Option



E22841-MW
LED Flush/Wall Mount
Finish: Matte White
Glass: Acrylic
31W LED (Lamps Included)
2,170 Lumens



E22843-MW
LED Semi-Flushmount
Finish: Matte White
Glass: Acrylic
43W LED (Lamps Included)
3,010 Lumens





QUAD



Cubist art reimagined through lighting, the Quad collection features suspended aluminum squares finished in a warm Bronze in multiple tiers, illuminated by high powered dimmable LEDs housed within the frame. The collection offers tremendous design flexibility with adjustable connectors for multiple configurations. The hanging illuminated squares serve as kinetic sculptures, adding a dimension of movement of the room.

QUAD



- 3000K Color Temperature
- Adjustable connectors allowing for various combinations
- Extruded Aluminum
- Dimmable



E22407-BZ
LED Pendant
Finish: Bronze
Glass: Acrylic
100W LED (Lamp Integrated)
7,000 Lumens
20.5" / 47.25" OAH



QUAD




E22405-BZ
LED Pendant
Finish: Bronze
Glass: Acrylic
55W LED (Lamp Integrated)
3,850 Lumens
11.75" / 47.25" OAH



QUAD

- 3000K Color Temperature
- Adjustable connectors allowing for various combinations
- Extruded Aluminum
- Dimmable



E22408-BZ
LED Flush Mount
Finish: Bronze
Glass: Acrylic
100W LED (Lamp Integrated)
6,500 Lumens




• Lights on



• Lights off



• Adjusted 3-tier



E20175-11MS
 LED Pendant
 Finish: Matte Silver
 Glass: Matte White
 64.2W LED (Lamps Included)
 4,494 Lumens
 10" / 130" OAH




CELLS

Intersecting circles form a collage of LED luminaires that become the focal point of the room. The collection features two pendants, as well as three sizes of modular ceiling fixtures in Matte Silver which can link together to form an artful array of light.



- Customizable, modular ceiling fixtures are easily linked together
- Acrylic diffuser to soften light output
- Up to 9 Mods controlled by one J box
- Dimmable LED
- 3000K Color Temperature
- CRI 80



E20177-11MS
 LED Pendant
 Finish: Matte Silver
 Glass: Matte White
 97.8W LED (Lamps Included)
 6,846 Lumens
 10" / 130" OAH




CELLS


The Cells collection is a modular system that allows for one unit to install on a powered outlet and up to 9 additional units of your choice to be added to the original module with the additional wire included inside each fixture. The additional wire moves from fixture to fixture through knockouts on the side. This system allows the user to create a sculpture of light on wall or ceiling sure to become the focal point in the room.




E20171-11MS
LED Flush/Wall Mounts
Finish: Matte Silver
Glass: Matte White
12W LED (Lamps Included)
840 Lumens



E20172-11MS
LED Flush/Wall Mounts
Finish: Matte Silver
Glass: Matte White
21.6W LED (Lamps Included)
1,512 Lumens



E20173-11MS
LED Flush/Wall Mounts
Finish: Matte Silver
Glass: Matte White
30.6W LED (Lamps Included)
2,142 Lumens





- Customizable, modular ceiling fixtures are easily linked together
- Acrylic diffuser to soften light output
- Up to 9 Mods controlled by one J box
- Dimmable LED
- 3000K Color Temperature
- CRI 80



1 x E20171-11MS
1 x E20172-11MS
1 x E20173-11MS



2 x E20171-11MS
2 x E20172-11MS
1 x E20173-11MS



2 x E20171-11MS
3 x E20172-11MS
2 x E20173-11MS

APOLLO

These Matte White circular pendants have the LED board concealed up inside the ring where it is invisible. The light bounces off an internal aluminum reflector and down onto the surface below. The result is a soft illumination without an ounce of glare.

E20226-MW
LED Pendant
Finish: Matte White
33W LED (Lamps Included)
2,310 Lumens
8" / 128" OAH



- Hidden high-powered LED source inside ring
- Internal Aluminum Reflector to direct light
- 3000K Color Temperature
- CRI 80

APOLLO



E20225-MW
 LED Pendant
 Finish: Matte White
 21W LED (Lamps Included)
 1,470 Lumens
 8" / 128" OAH






HOOPS

Multiple sizes of Polished Chrome hoops of light can be playfully arranged in various configurations for a power presentation. Continuous strips of LEDs are mounted inward towards the center of the hoop for an indirect display of light.

- Polished Chrome “hoops” adjustable to your preference
- LEDs mounted inward to provide indirect light
- 3000K Color Temperature
- CRI 80

HOOPS




E22716-PC
 LED Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 65.2W LED (Lamps Included)
 4,561 Lumens
 23" / 143" OAH



HOOPS



• Multiple arrangement options



E22715-PC
LED Pendant
Finish: Polished Chrome
Glass: Acrylic
30.6W LED (Lamps Included)
2,142 Lumens
12" / 130" OAH




HOOPS



- Polished Chrome “hoops” adjustable to your preference
- LEDs mounted inward to provide indirect light
- 3000K Color Temperature
- CRI 80



• Multiple arrangement options




E22714-PC
LED Pendant
Finish: Polished Chrome
Glass: Acrylic
24W LED (Lamps Included)
1,680 Lumens
12" / 130" OAH



HOOPS



- Polished Chrome “hoops” adjustable to your preference
- LEDs mounted inward to provide indirect light
- 3000K Color Temperature
- CRI 80




E22713-PC
LED Pendant
Finish: Polished Chrome
Glass: Acrylic
13.3W LED (Lamps Included)
932 Lumens
5" / 125" OAH



HOOPS



E22710-PC
 LED Wall Mount
 Finish: Polished Chrome
 Glass: Acrylic
 5.4W LED (Lamps Included)
 378 Lumens
 HCO: 1.58"



E22712-PC
 LED Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 8.6W LED (Lamps Included)
 605 Lumens
 5" / 125" OAH






TIMBALE

A series of round Die Cast rings, finished in Polished Chrome, are edge lit with high quality LEDs. Many of the rings are adjustable, allowing for unique design arrangements and light to be directed where needed.

TIMBALE

- Die Cast finished in Polished Chrome
- Edge lit with High quality LEDs
- Adjustable rings for directional lighting




E21148-01PC
LED Pendant
Finish: Polished Chrome
Glass: Acrylic
110W LED (Lamps Included)
9,900 Lumens
4.25" / 124.25" OAH



TIMBALE

- Die Cast finished in Polished Chrome
- Edge lit with High quality LEDs
- Adjustable rings for directional lighting




E21144-01PC
 LED Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 56.4W LED (Lamps Included)
 5,076 Lumens
 24" / 42.25" OAH

• **Telescopic Stem**




- Adjustable Die Cast rings to allow for unique design arrangements, and directional lighting.


TIMBALE




E21146-01PC
 LED Semi Flushmount
 Finish: Polished Chrome
 Glass: Acrylic
 110W LED (Lamps Included)
 9,900 Lumens




E21142-01PC
 LED Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 10.8W LED (Lamps Included)
 972 Lumens
 8.5" / 128.5" OAH




E21141-01PC
 LED Flush Mount
 Finish: Polished Chrome
 Glass: Acrylic
 10.8W LED (Lamps Included)
 972 Lumens



E21140-01PC
 LED Adjustable Flush Mount/Wall Mount
 Finish: Polished Chrome
 Glass: Acrylic
 6W LED (Lamps Included)
 540 Lumens






PALETTE

As if designed by Van Gogh, this collection features a flat aluminum palette, finished in Silver Foil paint. High powered 5 watt LED modules provide ample light and can be dimmed to set the mood. The ceiling fixture will work equally as well on the wall as a piece of art.

PALETTE



- 3000K Color Temperature
- High Powered, 5 Watt LED Modules
- Flat Aluminum palette finished in Silver Foil paint
- Dimmable



E20785-SF
9-Light Pendant
Finish: Silver Foil
9 x 5W LED (Lamps Included)
2,900 Lumens
3.25" / 124.25" OAH



PALETTE





E20784-SF
6-Light Pendant
Finish: Silver Foil
6 x 5W LED (Lamps Included)
2,100 Lumens
3.25" / 124.25" OAH





PALETTE

- 3000K Color Temperature
- Flush Mounts versatile for Wall Mounting
- High Powered, 5 Watt LED Modules
- Flat Aluminum palette finished in Silver Foil paint
- Dimmable



E20781-SF
 6-Light Flush/Wall Mount
 Finish: Silver Foil
 6 x 5W LED (Lamps Included)
 2,100 Lumens




E20782-SF
 9-Light Flush/Wall Mount
 Finish: Silver Foil
 9 x 5W LED (Lamps Included)
 2,900 Lumens



VOLT

This contemporary design features oval shaped die cast cups finished in Polished Chrome or Bronze which supports matching shape bubble glass shades. Each cup has dual LED modules which both light the glass shade above and provide down light below.




E22898-89BZ
E22898-89PC
16-Light Pendant
Finish: See Images
Glass: Etched/Bubble
16 x 3W LED (Lamps Included)
3,360 Lumens
8" / 120" OAH





- 3000K Color Temperature
- Indirect Up-Light and Direct Down-Light
- Solid oval shape, Etched Bubble Glass shades



E22897-89BZ
E22897-89PC
 16-Light Pendant
 Finish: See Images
 Glass: Etched/Bubble
 16 x 3W LED (Lamps Included)
 3,360 Lumens
 6" / 44.75" OAH


- Includes Two 6" stems ESTR06206BZ, PC
- Includes Six 12" stems ESTR06212BZ, PC



VOLT



LED 



Frame diagram and overall measurements

E22899-89BZ
E22899-89PC
16-Light Pendant
Finish: See Images
Glass: Etched/Bubble
16 x 3W LED (Lamps Included)
3,360 Lumens
6" / 44.75" OAH

- Includes Two 6" stems **ESTR06206BZ, PC**
- Includes Six 12" stems **ESTR06212BZ, PC**




- 3000K Color Temperature
- Indirect Up-Light and Direct Down-Light
- Etched Bubble Glass shades


VOLT




E22891-89BZ
 E22891-89PC
 2-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 2 x 3W LED (Lamps Included)
 420 Lumens
 HCO: 2.5"




E22892-89BZ
E22892-89PC
 4-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 4 x 3W LED (Lamps Included)
 840 Lumens
 HCO: 1.8"




E22893-89BZ
E22893-89PC
 6-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 6 x 3W LED (Lamps Included)
 1,260 Lumens
 HCO: 1.8"



E22894-89BZ
 E22894-89PC
 8-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 8 x 3W LED (Lamps Included)
 1,680 Lumens
 HCO: 1.8"




E22896-89BZ
E22896-89PC
 12-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 12 x 3W LED (Lamps Included)
 2,520 Lumens
 HCO: 1.8"



CYBORG


The Cyborg collection unites art and technology with a sci-fi nod to its form with chrome arms that grasp clear glass shades lit by Cree® LED modules in 3000K Color Temperature with dimmable drivers. Hanging crystals add a touch of glamour to this futuristic silhouette. The Cyborg collection makes a bold and imaginative statement in any living space.



E23062-18PC
 5-Light Flush Mount
 Finish: Polished Chrome
 Glass: Clear
 5 x 6W LED (Lamps Included)
 2,100 Lumens



E23067-18PC
 6-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 6 x 6W LED (Lamps Included)
 2,520 Lumens
 22" / 137.25" OAH



CYBORG


• Dimmable caps: 3000K Color Temperature



E23064-18PC
 4-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 4 x 6W LED (Lamps Included)
 1,680 Lumens
 7.5" / 125.5" OAH



4.75" []



E23061-18PC
 1-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 1 x 6W LED (Lamp Included)
 420 Lumens
 12.25" / 123.5" OAH




9" []
 4.75" []



E23065-18PC
 5-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 5 x 6W LED (Lamps Included)
 2,100 Lumens
 11.75" / 123.5" OAH



4.75" []





CONCENTRIC

Four Bronze concentric rings strategically placed in orbit to form a spherical lighting design as unique as it is functional. With the internal placement of LED strips the light moves both direct and indirect depending on where you are in relation to the fixture.


- Adjustable aluminum rings house high-powered integrated LEDs
- Spherical lighting design with acrylic diffuser
- 3000K Color Temperature
- CRI>80

CONCENTRIC



E24048-BZ
 LED Pendant
 Finish: Bronze
 80W LED (Lamps Included)
 3,675 Lumens
 39.25" / 75.25" OAH

- Includes One 6" stem ESTR06206BZ
- Includes Three 12" stems ESTR06212BZ




DONUTS

The Donut collection is a nod to retro, industrial and modern design sensibilities. Each fixture features floating round donuts of spun steel finished in a mirror like Polished Chrome. Clustered together, these rings house LEDs that glow upward into the white interior reflectors that move light indirectly out of the fixture without the glare of a direct light source.



E22599-PC


9-Light Pendant
Finish: Polished Chrome
9 x 16W LED (Lamps Included)
10,080 Lumens
4.75" / 124.25" OAH





LED is thrown upwards into the white interior reflectors of the rings. Those reflectors then move light indirectly out and into the room, without the glare of a direct source.

DONUTS

- Dimmable LED
- 3000K Color Temperature
- High Polished Chrome
- Even distribution of light



E22591-PC
 1-Light Pendant
 Finish: Polished Chrome
 1 x 16W LED (Lamp Included)
 1,120 Lumens
 4.75" / 124.25" OAH



E22596-PC
 6-Light Pendant
 Finish: Polished Chrome
 6 x 16W LED (Lamps Included)
 6,720 Lumens
 4.75" / 124.25" OAH



PANDORA

The Pandora collection is restrained Euro-styled elegance that adds architectural dimension with clean lines and fully dimmable turned aluminum candles with acrylic fonts lit by 3000K LED uplights. Available in a sleek square or rectangular black metallic platform, each fixture is paired with the same LEDs cleverly concealed beneath the table as down lights. The Pandora collection makes a subtle and sophisticated statement in any room of the house.

E22587-77BK

22-Light Pendant

Finish: Brushed Aluminum/Black



Glass: Acrylic

22 x 2.5W LED (Lamps Included)

3,850 Lumens

24.5" / 64.5" OAH

- Includes Two 6" stems ESTR06206BK
- Includes Six 12" stems ESTR06212BK



• Brushed Aluminum/Black metallic finish



• Fully dimmable aluminum candles with acrylic fonts



PANDORA

E22583-77BK
 8-Light Pendant
 Finish: Brushed Aluminum/Black
 Glass: Acrylic
 8 x 2.5W LED (Lamps Included)
 1,400 Lumens
 24.5" / 78.75" OAH

- Dimmable LED
- 3000K Color Temperature
- Up and down lights
- Aluminum candles with acrylic fonts
- Candles house LED up-lights




- Includes One 6" stem ESTR06206BK
- Includes Three 12" stems ESTR06212BK



E22585-77BK
 16-Light Pendant
 Finish: Brushed Aluminum/Black
 Glass: Acrylic
 16 x 2.5W LED (Lamps Included)
 3,150 Lumens
 24.5" / 61.5" OAH


- Includes Two 6" stems ESTR06206BK
- Includes Six 12" stems ESTR06212BK



BLADE

A thin blade of Bronze aluminum incorporates a micro size LED board recessed into the bottom. The result is a unique effect of light appearing on the surface below without a clear indication from where it is generated.

- Low-profile aluminum "blade" with integrated LED board recessed into bottom
- Dark Bronze finish
- 3000K Color Temperature



4.75" [



4.75" [



53.75"



E22906-BZ
LED Pendant
Finish: Bronze
36W LED (Lamps Included)
2,520 Lumens
7.5" / 125" OAH





BLADE



E22902-BZ
LED Pendant
Finish: Bronze
26W LED (Lamps Included)
1,820 Lumens
7.5" / 125" OAH



E22904-BZ
LED Pendant
Finish: Bronze
35W LED (Lamps Included)
2,450 Lumens
7.5" / 125" OAH



RHOMBUS

Large scale rectangular forms suspend gracefully in mid-air to fill a large space without a bulky appearance. LEDs are cleverly concealed in both the bottom and the top to provide a combination of up and down light. Available in your choice of Matte White or Bronze.




• Uplight



BZ Bronze



• Downlight



E22866-BZ
E22866-MW
LED Pendant
Finish: See Images
51W LED (Lamps Included)
3,570 Lumens
20.25" / 137.75" OAH




- Concealed LED in bottom of thin-profile rectangular forms
- Available in Matte White and Bronze finish
- 3000K Color Temperature

RHOMBUS



MW Matte White



E22864-BZ
 E22864-MW
 LED Pendant
 Finish: See Images
 43W LED (Lamps Included)
 3,010 Lumens
 17" / 134.5" OAH




QUANTUM

These Black aluminum pendants are unique in that they are formed as a tapered cylinder open at both the top and bottom. LEDs are mounted on the very top projecting down into a white acrylic diffuser, lining the inside of the pendant. The opening at the top provides up-light, as well as down-light.



E20908-BK
2-Light Pendant
Finish: Black
Glass: Acrylic
2 x 40W LED (Lamps Included)
5,600 Lumens
13.5" / 133.5" OAH




QUANTUM

- Black Aluminum pendants with tapered cylinder
- Open bottom and top to provide up and down-lighting
- White Acrylic diffuser
- CRI-80



E20906-BK
2-Light Pendant
Finish: Black
Glass: Acrylic
2 x 30W LED (Lamps Included)
3,500 Lumens
10.5" / 130.5" OAH






CHAOS

This contemporary collection features a cork screw configuration of Polished Chrome metal surrounding bands of 3000K LED. This eclectic approach to lighting design is sure to please those looking for a unique source of light.

- Unique functional sculptures of illumination
- Corkscrew bands with inset high-powered LEDs
- Diodes visible to create contemporary look
- 3000K Color Temperature
- CRI-80


CHAOS



E21417-PC
 LED Pendant
 Finish: Polished Chrome
 129.6W LED (Lamps Included)
 9,072 Lumens
 17" / 137" OAH



CHAOS




E21415-PC
LED Pendant
Finish: Polished Chrome
84.2W LED (Lamps Included)
5,897 Lumens
17" / 137" OAH



- Unique functional sculptures of illumination
- Corkscrew bands with inset high-powered LEDs
- Diodes visible to create contemporary look
- 3000K Color Temperature
- CRI-80

CHAOS



E21410-PC
 LED Flush Mount
 Finish: Polished Chrome
 90.7W LED (Lamps Included)
 6,350 Lumens



PUFFS

Soft forms of Matte White glass suspend from the ceiling like clouds moving through the sky. Columns of LEDs protrude down the middle of each shade to evenly illuminate the glass with a soft ambient light.




- Cloud-like forms of glass in Matte White finish
- Columns of LED inside glass provide soft, ambient light
- Available in three shapes with customizable multi-pendants
- 3000K Color Temperature
- CRI>80

PUFFS





E21129-MW
 14-Light Pendant
 Finish: Matte White
 Glass: Matte White
 67.2W LED (Lamps Included)
 4,704 Lumens
 10" / 130" OAH



PUFFS




E21127-MW
9-Light Pendant
Finish: Matte White
Glass: Matte White
43.2W LED (Lamps Included)
3,024 Lumens
10" / 130" OAH



- Cloud-like forms of glass in Matte White finish
- Columns of LED inside glass provide soft, ambient light
- Available in three shapes with customizable multi-pendants
- 3000K Color Temperature
- CRI>80

PUFFS




E21125-MW
 8-Light Pendant
 Finish: Matte White
 Glass: Matte White
 38.4W LED (Lamps Included)
 2,688 Lumens
 10" / 130" OAH



PUFFS

- Cloud-like forms of glass in Matte White finish
- Columns of LED inside glass provide soft, ambient light
- Available in three shapes with customizable multi-pendants
- 3000K Color Temperature
- CRI>80



E21124-MW
6-Light Pendant
Finish: Matte White
Glass: Matte White
28.8W LED (Lamps Included)
2,016 Lumens
10" / 130" OAH




PUFFS



E21121-MW
 1-Light Pendant
 Finish: Matte White
 Glass: Matte White
 4.8W LED (Lamps Included)
 336 Lumens
 10" / 130" OAH



E21120-MW
 1-Light Pendant
 Finish: Matte White
 Glass: Matte White
 4.8W LED (Lamps Included)
 336 Lumens
 8" / 128" OAH



E21122-MW
 1-Light Pendant
 Finish: Matte White
 Glass: Matte White
 4.8W LED (Lamps Included)
 336 Lumens
 7.75" / 127.5" OAH



SCEPTER


Slender beveled cut rods of bubble glass, illuminated by high power LED modules, suspend in an array of fashionable configurations. Available in Black Chrome with Clear bubble glass and Anodized Bronze with Champagne bubble glass.

SCEPTER

- Multi-faceted prisms with inner bubbles available in Clear or Champagne
- Finishes available in Black Chrome and Anodized Bronze
- 3000K Color Temperature



E32778-91BC
E32778-118BRZ
10-Light Pendant
Finish: See Images
Glass: See Images
75W LED (Lamps Included)
2,460 Lumens
140" OAH



• Clear bubble glass





• Champagne bubble glass

SCEPTER



E32775-91BC
E32775-118BRZ
5-Light Pendant
Finish: See Images
Glass: See Images
37.5W LED (Lamps Included)
1,230 Lumens
140" OAH




E32771-91BC
E32771-118BRZ
1-Light Pendant
Finish: See Images
Glass: See Images
7.5W LED (Lamps Included)
246 Lumens
20"/140" OAH



- Multi-faceted prisms with inner bubbles available in Clear or Champagne
- Finishes available in Black Chrome and Anodized Bronze
- 3000K Color Temperature


SCEPTER



E32779-91BC
E32779-118BRZ
 10-Light Pendant
 Finish: See Images
 Glass: See Images
 75W LED (Lamps Included)
 2,460 Lumens
 20"/140" OAH



SCEPTER



E32776-91BC
E32776-118BRZ
6-Light Pendant
Finish: See Images
Glass: See Images
45W LED (Lamps Included)
1,476 Lumens
20"/140" OAH




SCEPTER


- Multi-faceted prisms with inner bubbles available in Clear or Champagne
- Finishes available in Black Chrome and Anodized Bronze
- 3000K Color Temperature



E32770-91BC
E32770-118BRZ
 1-Light Wall Mount
 Finish: See Images
 Glass: See Images
 7.5W LED (Lamps Included)
 246 Lumens
 HCO: 7"



E32774-91BC
E32774-118BRZ
 4-Light Pendant
 Finish: See Images
 Glass: See Images
 30W LED (Lamps Included)
 984 Lumens
 20"/140" OAH





FIZZ |||


This forever popular collection is now better than ever. High output LEDs now illuminate the bubble glass pendants. The LED modules produce 20% more light, 90% less heat, 25% longer life, and 75% less energy than the previous halogen lamp. You also still have dimming capability, adding a personal touch to your space.

- 3000K Color Temperature
- Ribbed Acrylic rectangular prisms with inner bubbles
- Etched Bubble Glass shades
- Standard Lutron® CL™ or Leviton Dimmers recommended

FIZZ III



E22769-89BZ
E22769-89PC
 9-Light LED Pendant
 Finish: See Images
 Glass: Etched/Bubble
 9 x 7.5W LED (Lamps Included)
 2,214 Lumens
 135" OAH



FIZZ III




E22767-89BZ
E22767-89PC
7-Light Pendant
Finish: See Images
Glass: Etched/Bubble
7 x 7.5W LED (Lamps Included)
1,675 Lumens
135" OAH




- 3000K Color Temperature
- Ribbed Acrylic rectangular prisms with inner bubbles
- Etched Bubble Glass shades
- Standard Lutron® CL™ or Leviton Dimmers recommended

FIZZ III




E22761-89BZ
E22761-89PC
1-Light Pendant
Finish: See Images
Glass: Etched/Bubble
1 x 7.5W LED (Lamp Included)
238 Lumens
14" / 120" OAH



E22765-89BZ
E22765-89PC
5-Light Pendant
Finish: See Images
Glass: Etched/Bubble
5 x 7.5W LED (Lamps Included)
1,190 Lumens
135" OAH



FIZZ III



E22764-89BZ
E22764-89PC
5-Light Pendant
Finish: See Images
Glass: Etched/Bubble
5 x 7.5W LED (Lamps Included)
1,180 Lumens
14" / 120" OAH





- 3000K Color Temperature
- Ribbed Acrylic rectangular prisms with inner bubbles
- Etched Bubble Glass shades
- Standard Lutron® CL™ or Leviton Dimmers recommended

FIZZ III



E22760-89BZ
E22760-89PC
1-Light Wall Mount
Finish: See Images
Glass: Etched/Bubble
1 x 7.5W LED (Lamp Included)
235 Lumens
HCO:7"



E22763-89BZ
E22763-89PC
3-Light Pendant
Finish: See Images
Glass: Etched/Bubble
3 x 7.5W LED (Lamps Included)
710 Lumens
14" / 120" OAH






SOLITAIRE

Elegant beveled crystal, almond pentagone suspended inside clear glass cylinders, are brought to life by high powered 3W COB LEDs. These LEDs are cleverly concealed inside heat sink castings that are finished in Polished Chrome.

SOLITAIRE

- COB LED Technology
- 3000K Color Temperature
- CRI-80




E21116-18PC

6-Light Pendant
Finish: Polished Chrome
Glass: Clear
6 x 3W COB LED (Lamps Included)
1,980 Lumens
14.5" / 132" OAH



SOLITAIRE


- COB LED Technology
- 3000K Color Temperature
- CRI-80



E21115-18PC
5-Light Pendant
Finish: Polished Chrome
Glass: Clear
5 x 3W COB LED (Lamps Included)
1,650 Lumens
14.5" / 132" OAH




SOLITAIRE



E21113-18PC
 3-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 3 x 3W COB LED (Lamps Included)
 990 Lumens
 14.5" / 132" OAH



E21111-18PC
 1-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 1 x 3W COB LED (Lamp Included)
 330 Lumens
 14.5" / 132" OAH





HILITE


These low profile pendants, featuring edge lit technology for soft even illumination, are constructed of die cast aluminum and finished in your choice of Polished Chrome or Bronze. Frosted acrylic fonts adorn the top of each pendant and are illuminated by LED, located in the top casting.

- Edge lit technology for soft even illumination
- Die cast Aluminum available in your choice of Polished Chrome or Bronze
- Frosted acrylic fonts adorn the top of each pendant, illuminated by LEDs

HILITE



E21169-01PC
E21169-01BZ
 9-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 9 x 7.2W LED (Lamps Included)
 5,832 Lumens
 5.75" / 125.75" OAH




HILITE


- Edge lit technology for soft even illumination
- Die cast Aluminum available in your choice of Polished Chrome or Bronze
- Frosted acrylic fonts adorn the top of each pendant, illuminated by LEDs




E21160-01PC
E21160-01BZ
 1-Light Flush Mount/Wall Mount
 Finish: See Image
 Glass: Frosted Acrylic
 1 x 10.8W LED (Lamp Included)
 972 Lumens
 HCO: 2.4"



E21161-01PC
E21161-01BZ
 1-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 1 x 7.2W LED (Lamp Included)
 648 Lumens
 5.75" / 125.75" OAH




E21162-01PC
E21162-01BZ
 1-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 1 x 12W LED (Lamp Included)
 1,080 Lumens
 7" / 127" OAH






E21166-01PC
E21166-01BZ
 6-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 69.6W LED (Lamps Included)
 6,264 Lumens
 8.5" / 128" OAH



E21165-01PC
E21165-01BZ
 5-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 5 x 7.2W LED (Lamps Included)
 3,240 Lumens
 5.75" / 126" OAH





POLKA


Polished Chrome hardware accentuates heavy Clear pressed glass shades with a dimple pattern. Excellent light is projected to the surface below by means of 3 watt LED modules in a soft, warm 3000K color temperature.

POLKA

- COB LED Technology
- Clear pressed glass, with a dimple pattern
- 3000K Color Temperature




E20779-18PC
9-Light Pendant
Finish: Polished Chrome
Glass: Clear
9 x 3W COB LED (Lamps Included)
2,970 Lumens
8" / 128" OAH



POLKA


- COB LED Technology
- Clear pressed glass, with a dimple pattern
- 3000K Color Temperature




E20775-18PC
5-Light Pendant
Finish: Polished Chrome
Glass: Clear
5 x 3W COB LED (Lamps Included)
1,650 Lumens
8" / 128" OAH




• Clear pressed glass, with a dimple pattern




E20771-18PC
 1-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 1 x 3W COB LED (Lamp Included)
 330 Lumens
 8" / 128" OAH



E20770-18PC
 9-Light Flush Mount
 Finish: Polished Chrome
 Glass: Clear
 9 x 3W COB LED (Lamps Included)
 2,970 Lumens



E20773-18PC
 3-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 3 x 3W COB LED (Lamps Included)
 990 Lumens
 8" / 128" OAH





PARASOL

Domes of metal rings, finished in Polished Chrome, are inset with beveled crystals to create these delicate parasols. High powered LED bulbs shine indirectly up into the inside of each shade, providing gentle illumination and vivid sparkle from the crystal.


PARASOL

- Domes of Polished Chrome rings, inset with clear, beveled crystals
- Indirect, high powered LED's provide a gentle illumination



E24499-20PC

9-Light Pendant
Finish: Polished Chrome
Glass: Crystal
9 x 4W LED (Lamps Included)
2,880 Lumens
8" / 128" OAH




PARASOL

- Domes of Polished Chrome rings, inset with clear, beveled crystals
- Indirect, high powered LED's provide a gentle illumination



PARASOL



E24495-20PC
5-Light Pendant
Finish: Polished Chrome
Glass: Crystal
5 x 4W LED (Lamps Included)
1,600 Lumens
8" / 128" OAH




PARASOL

- Domes of Polished Chrome rings, inset with clear, beveled crystals
- Indirect, high powered LED's provide a gentle illumination



E24491-20PC
 1-Light Pendant
 Finish: Polished Chrome
 Glass: Crystal
 1 x 4W LED (Lamp Included)
 320 Lumens
 8" / 128" OAH




E24497-20PC
 1-Light Pendant
 Finish: Polished Chrome
 Glass: Crystal
 1 x 15W LED (Lamp Included)
 1,050 Lumens
 16" / 136" OAH



PARASOL



E24496-20PC
5-Light Pendant
Finish: Polished Chrome
Glass: Crystal
5 x 4W LED (Lamps Included)
1,600 Lumens
8" / 128" OAH






SENSE II

The Sense II collection lends an air of cosmic mysticism with Mirror Chrome plate glass shades that are hand etched for added dimension. The sinuous curves hint at eccentric glamour and feature modern technology with its state-of-the-art Smith & Kole 12-volt transformer, among the best in the market. This sculptural fixture commands the center of attention, anchoring the look of a living space.

SENSE II

- G9, Xenon Lamps Included
- Mirror Chrome Plated
- Hand Etched details
- Teardrop Crystal pendants trim detail






E21406-81PC
6-Light Pendant
Finish: Polished Chrome
Glass: Mirror Chrome
6 x 40W G9 (Lamps Included)
3,000 Lumens
11.5" / 128" OAH

SENSE II


- G9, Xenon Lamps Included
- Mirror Chrome Plated
- Hand Etched details
- Teardrop Crystal pendants trim detail




E21405-81PC
 5-Light Pendant
 Finish: Polished Chrome
 Glass: Mirror Chrome
 5 x 40W G9 (Lamps Included)
 2,500 Lumens
 11.25" / 128" OAH




E21409-81PC
 1-Light Wall Mount
 Finish: Polished Chrome
 Glass: Mirror Chrome
 1 x 40W G9 (Lamp Included)
 500 Lumens
 HCO: 3.5"



E21399-81PC
 3-Light Flush Mount
 Finish: Polished Chrome
 Glass: Mirror Chrome
 3 x 40W G9 (Lamps Included)
 1,500 Lumens




E21401-81PC
 5-Light Flush Mount
 Finish: Polished Chrome
 Glass: Mirror Chrome
 5 x 40W G9 (Lamps Included)
 2,500 Lumens



E21403-81PC
 6-Light Flush Mount
 Finish: Polished Chrome
 Glass: Mirror Chrome
 6 x 40W G9 (Lamps Included)
 3,000 Lumens

APEX

This Danish modern collection of large scale pendants is on trend. Available in two sizes and three finishes, White, Brick, and Steel Blue, these pendants are not only functional but also add a splash of color to any space.



E20638-BR
E20638-SB
E20638-WT

1-Light Pendant
Finish: See Images
1 x 60W MB Lamp
672 Lumens
14.5" / 132" OAH



APEX


- Large scale pendants
- Three color options, for a splash of color
- Incandescent



-BR Brick




-SB Steel Blue



-WT White

E20639-BR
E20639-SB
E20639-WT
1-Light Pendant
Finish: See Images
1 x 60W MB Lamp
672 Lumens
20" / 138" OAH




SOLAR

The Solar collection embraces metallic trends with its Mirror Chrome or Mirror Copper plated blown glass orbs with interior Chrome finishes, available in three size options. The celestial inspired globes can morph from retro to modern styling. The Solar collection is the perfect companion to metallic infused furnishings and decorative accents across all styles from industrial to collected-eclectic.




E20635-81PC
E20635-151PC
1-Light Pendant
Finish: See Image
1 x 100W MB
1,150 Lumens
18" / 118" OAH




SOLAR


- Blown glass
- Choice of Mirror Chrome or Mirror Copper
- Interior Chrome plated
- Incandescent



E20633-81PC
E20633-151PC
 1-Light Pendant
 Finish: See Image
 1 x 100W MB
 1,150 Lumens
 16" / 118" OAH



• Blown glass, with interior Chrome finish



E20631-81PC
 E20631-151PC
 1-Light Pendant
 Finish: See Image
 1 x 100W MB
 1,150 Lumens
 14" / 118" OAH



STAGE

Inspired by stage lighting, this functional collection will display plenty of light wherever needed. This refined rendition features a soft round body finished in Satin Aluminum, Chrome hardware accents, and is powered by a dimmable 15 watt COB LED.



E20833-SA


1-Light Pendant

Finish: Satin Aluminum

1 x 15W COB LED (Lamp Included)


1,650 Lumens

22" / 142" OAH




- COB technology
- Dimmable 15 watt LED
- Satin Aluminum finish, Chrome hardware accents



STAGE




E20835-SA
 1-Light Floor Lamp
 Finish: Satin Aluminum
 1 x 15W COB LED (Lamp Included)
 1,650 Lumens



E20831-SA
 1-Light Semi Flushmount
 Finish: Satin Aluminum
 1 x 15W COB LED (Lamp Included)
 1,650 Lumens




• Satin Aluminum finish




• Chrome hardware accent

ARHAUS


The Arhaus collection creates intrigue as a visual paradox, making unconventional use of solid wood as hanging pendant shades. The solid, lathe turned pendants of sculpted wood shapes are lit with dimmable 3 Watt LED modules in 3000K and straddle the design spectrum from industrial to modern and rustic luxe. For a fresh take on the traditional chandelier, group several pendants together at various heights in a soft organic cluster.



E20752-NWD
1-Light Pendant
Finish: Natural Wood
1 x 3W LED (Lamp Included)
210 Lumens
10.5" / 118" OAH



E20754-NWD
1-Light Pendant
Finish: Natural Wood
1 x 3W LED (Lamp Included)
210 Lumens
10" / 118" OAH





ARHAUS

- Dimmable LED
- 3000K Color Temperature
- Solid, lathe turned heads of Ash wood



E20753-NWD
1-Light Pendant
Finish: Natural Wood
1 x 3W LED (Lamp Included)
210 Lumens
11.5" / 118" OAH



E20751-NWD
1-Light Pendant
Finish: Natural Wood
1 x 3W LED (Lamp Included)
210 Lumens
8" / 118" OAH



CILANDRO LED


This ever popular collection is now available in LED. Four integrated LED boards are enclosed with a commercial grade dimmable driver for ultimate function and long life. Great for commercial or residential applications, Matte White glass twist locks into a steel base finished in Satin Nickel for a clean modern look.

- 3000K Color Temperature
- Four integrated LED boards enclosed with a commercial grade dimmable driver
- Matte White glass twist locks into a steel base
- CRI 80




E63109-11SN
LED Pendant
Finish: Satin Nickel
Glass: Matte White
4 x 2.4W LED (Lamp Included)
672 Lumens
24" / 134" OAH

- Glass is enclosed
- Dry Location only




E63106-11SN
LED Wall Mount
Finish: Satin Nickel
Glass: Matte White
4 x 2.4W LED (Lamp Included)
672 Lumens
HCO:10"

- Glass is enclosed
- Suitable for Damp location




E63107-11SN
LED Wall Mount
Finish: Satin Nickel
Glass: Matte White
8 x 2.4W LED (Lamp Included)
1,344 Lumens
HCO:2.5"

- Glass is enclosed
- Suitable for Damp location



RONDELLE

Inspired by the small disks of glass that are used as ornaments in stained glass windows, the Rondelle single light White or Red pendants presents a simple and clean cylindrical form. The Rondelle possess matching glass canopy accented by Polished Chrome hardware and featuring adjustable height for maximum adaptability. Consider it the perfect lighting solution for bar, bathroom, kitchen island or pool table.



E20841-01
E20841-03
 1-Light Pendant
 Finish: Polished Chrome
 Glass: See Images
 1 x 60W MB Lamp
 672 Lumens
 24" / 120" OAH

• Matching glass canopy



CAPS

Bold color combined with simple curves defines the essence of the Caps collection. The exquisite pendants with matching glass canopy of Caps are available in White and Red. Equally suited for residential or commercial applications, you can either arrange the pendants flying solo or in multiple formations.




E20851-01
E20851-03
 1-Light Pendant
 Finish: Polished Chrome
 Glass: See Images
 1 x 100W MB Lamp
 1,150 Lumens
 18" / 120" OAH

• Matching glass canopy



GEM

With the illusion of floating on air, the Gem Collection offers a touch of mystery to any room. Intertwined metal cubes are encased by clear crystal cubes, allowing xenon light to shine from within and bursting out through the embellished crystal.



E22836-18SVPC
E22836-18PCPC
 6-Light Flush Mount
 Finish: Polished Chrome
 Glass: Clear
 6 x 40W G9 (Lamps Included)
 3,000 Lumens




E22838-18SVPC
E22838-18PCPC
 4-Light Flush Mount
 Finish: Polished Chrome
 Glass: Clear
 4 x 40W G9 (Lamps Included)
 1,600 Lumens





• Standard Dimmable




E22830-18SVPC
E22830-18PCPC
 1-Light Wall Mount
 Finish: Polished Chrome
 Glass: Clear
 1 x 60W G9 (Lamp Included)
 500 Lumens
 HCO: 2"




E22832-18SVPC
E22832-18PCPC
 2-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Clear
 2 x 40W G9 (Lamps Included)
 1,000 Lumens
 HCO: 2"



E22833-18SVPC
E22833-18PCPC
 3-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Clear
 3 x 40W G9 (Lamps Included)
 1,500 Lumens
 HCO: 2"



E22834-18SVPC
E22834-18PCPC
 4-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Clear
 4 x 40W G9 (Lamps Included)
 2,000 Lumens
 HCO: 2"





E22835-18SVPC
E22835-18PCPC
 5-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Clear
 5 x 40W G9 (Lamps Included)
 2,500 Lumens
 HCO: 2"



INCA

Legendary meets contemporary with the Inca Collection. Reminiscent of the mythical tales of Incan treasures, the fixtures offer brilliantly shining crystal enclosed within a precision laser-cut sheath that cannot be duplicated. The glow of the LED light from within casts a beautifully radiant shine that adorns the outer permeable layer.




E21336-61BZ
E21336-61PC
4-Light LED Large Wall Sconce
Finish: See Images
Glass: Acrylic
4 x 6W LED (Lamps Included)
1,280 Lumens

- Made with Steel grade 304
- Suitable for Indoor or Outdoor Locations




- 304 Grade Stainless Steel
- Features a White Acrylic liner and diffuser
- Suitable for Indoor and Outdoor locations




E21335-61BZ
E21335-61PC
 4-Light LED Medium Wall Sconce
 Finish: See Images
 Glass: Acrylic
 4 x 6W LED (Lamps Included)
 1,280 Lumens

- Made with Steel grade 304
- Suitable for Indoor or Outdoor Locations



E21333-61BZ
E21333-61PC
 2-Light LED Small Wall Sconce
 Finish: See Images
 Glass: Acrylic
 2 x 6W LED (Lamps Included)
 640 Lumens

- Made with Steel grade 304
- Suitable for Indoor or Outdoor Locations




ALUMILUX AL

The Alumilux collection of high quality wall sconces are sure to impress. European inspired design, machined out of blocks of solid Aluminum, give these sconces both the look and quality expected for the discriminate buyer. High powered LEDs drive the light in dramatic fashion and many are approved for wet location applications.



SA Satin Aluminum




E41310-BZ
E41310-SA
6-Light LED Wall Mount
Finish: Satin Aluminum
6 x 1.8W LED (Lamps Included)
560 Lumens
HCO: 2.25"

• Wet and Dry Location



BZ Bronze




E41308-BZ
E41308-SA
2-Light LED Wall Mount
Finish: See Images
2 x 3W LED (Lamps Included)
320 Lumens
HCO: 2.25"

• Wet and Dry Location



WT White




E41302-SA
E41302-WT
18-Light LED Wall Mount
Finish: See Images
18 x 0.3W LED (Lamps Included)
445 Lumens
HCO: 2.25"

• Wet and Dry Location



SA Satin Aluminum





E41307-SA
E41307-WT
5-Light LED Wall Mount
Finish: See Images
5 x 1W LED (Lamps Included)
430 Lumens
HCO: 12.5"

• Dry Location Only



- Lamps Included
- Energy Efficient
- Wet and Dry Locations


ALUMILUX DC




E41413-BZ
 3-Light LED Wall Mount
 Finish: Bronze
 3 x 2W LED (Lamps Included)
 420 Lumens
 HCO: 3.5"




• Front view



E41425-PL
 4-Light LED Wall Mount
 Finish: Platinum
 4 x .3W LED (Lamps Included)
 840 Lumens
 HCO: 4.3"



• Front view



E41424-PL
 3-Light LED Wall Mount
 Finish: Platinum
 3 x .3W LED (Lamps Included)
 630 Lumens
 HCO: 6"



• Shown with lights on

• Shown with lights on



ALUMILUX AL





SA Satin Aluminum



• Vertical mount

E41324-BZ
E41324-SA
 27-Light LED Wall Mount
 Finish: See Image
 27 x 0.3W LED (Lamps Included)
 547 Lumens
 HCO: 2.16"


• Wet and Dry Location



SA Satin Aluminum

E41323-BZ
E41323-SA
 9-Light LED Wall Mount
 Finish: See Image
 9 x 0.3W LED (Lamps Included)
 547 Lumens
 HCO: 2.16"

• Wet and Dry Location




SA Satin Aluminum



• View from opposite side


E41318-BZ
E41318-SA
 2-Light LED Wall Mount
 Finish: See Image
 2 x 3W LED (Lamps Included)
 420 Lumens
 HCO: 3.44"

• Wet and Dry Location




ALUMILUX AL

- Lamps Included
- Energy Efficient
- Wet and Dry Locations



SA Satin Aluminum




E41300-BZ
E41300-SA
 7-Light LED Wall Mount
 Finish: See Images
 7 x 1W LED (Lamps Included)
 560 Lumens
 HCO: 5"

- Wet and Dry Location



SA Satin Aluminum




E41321-BZ
E41321-SA
 28-Light LED Wall Mount
 Finish: See Image
 28 x 0.3W LED (Lamps Included)
 440 Lumens
 HCO: 3.72"

- Wet and Dry Location



BZ Bronze



E41319-BZ
E41319-SA
 1-Light LED Wall Mount
 Finish: See Images
 1 x 3W LED (Lamp Included)
 210 Lumens
 HCO: 2.16"

- Wet and Dry Location




ALUMILUX DC

European designed outdoor lighting unique to the North American market and exclusively offered to you by ET2. Cast aluminum construction with multi functional design offers a different and fun approach to exterior lighting. Multiple powder coated finishes to choose from all powered with top of the line LEDs.



E41409-09BZ
 2-Light LED Wall Mount
 Finish: Bronze
 Glass: Opal
 1 x 3.5W + 1 x 1W LED (Lamps Included)
 315 Lumens
 HCO: 4.2"



• Wet and Dry Location



• View from side

E41407-BZ
 5-Light LED Wall Mount
 Finish: Bronze
 5 x 1W LED (Lamps Included)
 350 Lumens
 HCO: 3.75"

• Wet and Dry Location




• Lights on



• Lights on


- Lamps Included
- Energy Efficient
- 3000K Color Temperature
- Wet and Dry Locations

ALUMILUX DC




E41414-PL
 3-Light LED Wall Mount
 Finish: Platinum
 3 x .3W LED (Lamps Included)
 630 Lumens
 HCO: 2.25"

• Wet and Dry Location




• Rotates for directional light



E41410-BZPL
 3-Light LED Wall Mount
 Finish: Bronze/Platinum
 3 x 1W LED (Lamps Included)
 210 Lumens
 HCO: 3"

• Wet and Dry Location



E41411-BZPL
 3-Light LED Wall Mount
 Finish: Bronze/Platinum
 3 x 1W LED (Lamps Included)
 210 Lumens
 HCO: 4.75"

• Wet and Dry Location



• Lights on



• Lights on

ALUMILUX DC


- Lamps Included
- Energy Efficient
- 3000K Color Temperature
- Wet and Dry Locations



• View from top


E41420-BZ
6-Light LED Wall Mount
Finish: Bronze
6 x 2.5W LED (Lamps Included)
1,050 Lumens
HCO: 2.25"

- Wet and Dry Location



E41415-DG
6-Light LED Wall Mount
Finish: Dark Gray
6 x 1W LED (Lamps Included)
420 Lumens
HCO: 5.5"

- Wet and Dry Location




- Work on all 12V systems
- Includes ground spike anchor bolts
- Includes LV cable connector
- LED Garden options

ALUMILUX DC




E41406-BZ
 9-Light LED Pathway Light
 Finish: Bronze
 9 x .5W LED (Lamps Included)
 315 Lumens

- Wet and Dry Location




E41421-BZ
 6-Light LED Pathway Light
 Finish: Bronze
 6 x 2.5W LED (Lamps Included)
 1,050 Lumens

- Wet and Dry Location



E41416-DG
 6-Light LED Pathway Light
 Finish: Dark Gray
 6 x 1W LED (Lamps Included)
 420 Lumens

- Wet and Dry Location




- Includes ground spike anchor bolts

ALUMILUX DC




- LED Garden options
- 3000K Color Temperature
- Work on all 12V systems
- Includes ground spike anchor bolts
- Includes LV cable connector
- Wet and Dry Locations

• Adjustable to 90°



E41419-BZ
 3-Light LED Pathway Light
 Finish: Bronze
 3 x 1W LED (Lamps Included)
 210 Lumens

- Wet and Dry Location



E41418-BZ
 9-Light LED Pathway Light
 Finish: Bronze
 9 x .5W LED (Lamps Included)
 315 Lumens

- Wet and Dry Location



- Includes ground spike anchor bolts

ALUMILUX AL

These sleek solid aluminum construction and high quality LED garden lights will enhance the beauty of any home's walkway, pathway or garden. Lighting the way with energy efficient 12 volt system. Each fixture is supplied with a universal connector that will attach to a direct burial cable. There is an optional installation by a ground stake or an anchor bolts.

- Work on all 12V systems
- Includes ground spike anchor bolts
- Includes LV cable connector
- LED Garden options






SA Satin Aluminum



SA Satin Aluminum



SA Satin Aluminum



- Includes ground spike anchor bolts


ALUMILUX AL

• Suitable for Wet Locations




SA Satin Aluminum

E41363-BZ
E41363-SA
2-Light LED
Finish: See Image
2 x 1W LED (Lamps Included)
140 Lumens




SA Satin Aluminum

E41366-BZ
E41366-SA
18-Light LED
Finish: See Image
18 x 0.3W LED (Lamps Included)
298 Lumens



SA Satin Aluminum

E41364-BZ
E41364-SA
1-Light LED
Finish: See Image
1 x 3W LED (Lamp Included)
210 Lumens



- Work on all 12V systems
- Includes ground spike anchor bolts
- Includes LV cable connector
- LED Garden options
- Suitable for Wet Locations

ALUMILUX AL






SA Satin Aluminum



BZ Bronze



SA Satin Aluminum



- Includes ground spike anchor bolts

INDEX

E20171.....	29	E20841.....	118	E21335.....	122
E20172.....	29	E20851.....	118	E21336.....	121
E20173.....	29	E20906.....	64	E21399.....	108
E20175.....	27	E20908.....	63	E21401.....	108
E20177.....	28	E21111.....	90	E21403.....	108
E20225.....	32	E21113.....	90	E21405.....	107
E20226.....	31	E21115.....	89	E21406.....	106
E20631.....	112	E21116.....	88	E21409.....	107
E20633.....	112	E21120.....	74	E21410.....	68
E20635.....	111	E21121.....	74	E21415.....	67
E20638.....	109	E21122.....	74	E21417.....	66
E20639.....	110	E21124.....	73	E22405.....	25
E20691.....	12	E21125.....	72	E22407.....	24
E20693.....	12	E21127.....	71	E22408.....	26
E20695.....	11	E21129.....	70	E22453.....	16
E20697.....	10	E21140.....	42	E22455.....	16
E20751.....	116	E21141.....	42	E22456.....	16
E20752.....	115	E21142.....	42	E22572.....	8
E20753.....	116	E21144.....	41	E22574.....	8
E20754.....	115	E21146.....	42	E22576.....	6
E20770.....	98	E21148.....	40	E22578.....	7
E20771.....	98	E21160.....	93	E22583.....	58
E20773.....	98	E21161.....	93	E22585.....	58
E20775.....	97	E21162.....	93	E22587.....	57
E20779.....	96	E21165.....	94	E22591.....	56
E20781.....	46	E21166.....	94	E22596.....	56
E20782.....	46	E21169.....	92	E22599.....	55
E20784.....	45	E21172.....	4	E22710.....	38
E20785.....	44	E21174.....	4	E22712.....	38
E20831.....	114	E21176.....	3	E22713.....	37
E20833.....	114	E21178.....	2	E22714.....	36
E20835.....	114	E21333.....	122	E22715.....	35

INDEX

E22716.....	34	E22897.....	48	E41321.....	126
E22760.....	86	E22898.....	47	E41323.....	125
E22761.....	84	E22899.....	49	E41324.....	125
E22763.....	86	E22902.....	60	E41350.....	134
E22764.....	85	E22904.....	60	E41360.....	132
E22765.....	84	E22906.....	59	E41363.....	133
E22767.....	83	E23061.....	52	E41364.....	133
E22769.....	82	E23062.....	51	E41365.....	134
E22820.....	14	E23064.....	52	E41366.....	133
E22822.....	14	E23065.....	52	E41367.....	132
E22824.....	13	E23067.....	51	E41369.....	134
E22830.....	120	E24048.....	54	E41371.....	132
E22832.....	120	E24491.....	103	E41406.....	130
E22833.....	120	E24493.....	101	E41407.....	127
E22834.....	120	E24495.....	102	E41409.....	127
E22835.....	120	E24496.....	104	E41410.....	128
E22836.....	119	E24497.....	103	E41411.....	128
E22838.....	119	E24499.....	100	E41413.....	124
E22840.....	22	E32770.....	80	E41414.....	128
E22841.....	22	E32771.....	77	E41415.....	129
E22843.....	22	E32774.....	80	E41416.....	130
E22845.....	21	E32775.....	77	E41418.....	131
E22847.....	20	E32776.....	79	E41419.....	131
E22848.....	19	E32778.....	76	E41420.....	129
E22849.....	18	E32779.....	78	E41421.....	130
E22864.....	62	E41300.....	126	E41424.....	124
E22866.....	61	E41302.....	123	E41425.....	124
E22891.....	50	E41307.....	123	E63106.....	117
E22892.....	50	E41308.....	123	E63107.....	117
E22893.....	50	E41310.....	123	E63109.....	117
E22894.....	50	E41318.....	125		
E22896.....	50	E41319.....	126		

FINISHES, GLASS, SHADES

Code	Finish
BC	Black Chrome
BK	Black
BR	Brick
BRZ	Anodized Bronze
BZ	Bronze
BZPL	Bronze / Platinum
DG	Dark Grey
MS	Metallic Silver
MW	Matte White
NWD	Natural Wood
OI	Oil Rubbed Bronze
PC	Polished Chrome
PCBK	Polished Chrome / Black
PCWT	Polished Chrome/White
PL	Platinum
PLPC	Platinum / Polished Chrome
SA	Satin Aluminum
SB	Steel Blue
SF	Silver Foil
SN	Satin Nickel
WT	White

Code	Glass
01	White
02	Black
03	Red
04	Green
05	Amber
08	Red Gloss
09	Frost White
10	Clear/White
11	Matte White
13	White Ripple
14	Amber Ripple
18	Clear
19	Lead - Glass
20	Crystal
24	Clear
25	Clear/Amber
26	Amber Murano
28	Clear Murano
39	Grey Ripple
50	Black Amber Swirl
51	Black Zebra
53	Conch
54	Translucent Frost
56	Chocolate Mousse
61	White
69	Silver Plate
75	Clear Acrylic
78	Mesh

Code	Glass
79	Threaded
81	Mirror Chrome
83	Clear Acrylic
85	Opal White
86	Frosted Speckled
87	Chocolate Swirl
88	Snow White
89	Etched/Bubble
90	Frosted
91	Bubble
93	Clear/Frosted
94	Cognac
101	White Lava
102	Amber Lava
103	Gold Lava
104	Amber Leopard
105	White Leopard
106	Amber Cloud
107	Cherry Swirl
108	Grape Swirl
109	Tangerine Swirl
111	Red Spiral
112	White Spiral
113	White Cirrus
114	Sunset
118	Champagne
132	Sky Blue
136	Champagne
138	Smoke
140	Graduating Blue
141	Graduating Amber
142	Graduating Smoke
146	Clear/Mirror
148	Multi Color
151	Mirror Copper
FT	Frosted

Code	Shade
69	Silver Plated
78	Mesh
93	Aluminum/Red
94	Aluminum/Green
97	Black Chain
120	Silver Sheer
AL	Aluminum
BR	Brushed Aluminum
GC	Grass Cloth
PC	Polished Chrome
SW	Steel Web
WL	White Linen
WW	White Weave

LAMPING GUIDE

Linedrawings	Item	Type	Base	Watt	Color	Description
	EBUCF-CFQ13-G24Q-1-827	CF	G24q-1	13	SW	CFL Quad 4 Pin G24q-1 Bulb, 2700K
	EBUCF-CFQ18-G24Q-2-827	CF	G24q-2	18	SW	CFL Quad 4 Pin G24q-2 Bulb, 2700K
	EBUCF-CFQ13-GX23-2-827	CF	GX23-2	13	SW	CFL Quad Bi-Pin GX23-2 Bulb, 2700K
	EBUCF-FT18-2G11-827	CF	2G11	18	SW	CFL Twin 4 Pin 2G11 Bulb, 2700K
	EBUCF-FT18-2G11-830	CF	2G11	18	SW	CFL Twin 4 Pin 2G11 Bulb, 3000K
	EBUCF-FT36-2G11-830	CF	2G11	36	SW	CFL Twin 4 Pin 2G11 Bulb, 3000K
	EBUF-F21T5-827	F	T5	21	SW	FL T5 Linear Mini Bi-Pin Bulb, 2700K 34"L
	EBUF-F21T5-830	F	T5	21	SW	FL T5 Linear Mini Bi-Pin Bulb, 2700K 34"L
	EBUF-F24T5-835	F	T5	24	SW	FL T5 Linear Mini Bi-Pin Bulb, 3500K 22"L
	EBUF-F39T5-835	F	T5	39	SW	FL T5 Linear Mini Bi-Pin Bulb, 3500K 34"L
	EBUF-SP13-GU24-827	F	GU24	13	SW	FL Spiral GU24 Bulb, 2700K
	EBUF-SP18-GU24-827	F	GU24	18	SW	FL Spiral GU24 Bulb, 2700K
	EBUF-SPLP13-GU24-827	F	GU24	13	SW	FL Low Profile Spiral GU24 Bulb, 2700K
	EBUF-SPLP18-GU24-827	F	GU24	18	SW	FL Low Profile Spiral GU24 Bulb, 2700K
	EBUH-35W-GU10-CL-120V	H	GU10	35	CL	Halogen GU10 110-130V, Clear Bulb
	EBUH-50W-GU10-CL-120V	H	GU10	50	CL	Halogen GU10 110-130V, Clear Bulb
	EBUH-50W-PAR20-FL-CL-120V	H	PAR20	50	CL	Halogen PAR20, 120V, Clear Bulb
	EBUI-60W-T10-E26-IF-120V	I	MB	60	IF	Incandescent MB T10 120V, Inside Frost Bulb
	EBUL-.2W-G3-CL-12V	L	G3	0.2	CL	LED G3, 3500K 12V, Clear Bulb
	EBUL-1.5W-G4-CL-12V	L	G4	1.5	CL	LED G4, 3000K 12V, Clear Bulb (See Restriction Supp Des)
	EBUL-2.9W-G9-CL-120V	L	G9	2.9	CL	LED G9 3500K 120V, Clear Bulb
	EBUL-2.9W-G9-CL-120V-827	L	G9	2.9	CL	LED G9 2700K 120V, Clear Bulb
	EBUL-3W-MR11-CL-12V	L	MR11	3	CL	LED MR11 3000K 12V, Clear Bulb
	EBUL-3W-MR16-FL-CL-12V	L	MR16	3	CL	LED MR16 3000K 12V, Clear Bulb
	EBUX-20W-G4-CL-12V	X	G4	20	CL	Xenon Bi-Pin G4 12V, Clear Bulb
	EBUX-20W-G4-FT-12V	X	G4	20	FT	Xenon Bi-Pin G4 12V, Frosted Bulb
	EBUX-35W-G4-CL-12V	X	G4	35	CL	Xenon Bi-Pin G4 12V, Clear Bulb
	EBUX-35W-G6.35-CL-12V	X	G6.35	35	CL	Xenon Bi-Pin G6.35 12V, Clear Bulb
	EBUX-35W-G6.35-FT-12V	X	G6.35	35	FT	Xenon Bi-Pin GY6.35 12V, Frosted Bulb
	EBUX-50W-G6.35-CL-12V	X	G6.35	50	CL	Xenon Bi-Pin G6.35 12V, Clear Bulb
	EBUX-50W-G6.35-FT-12V	X	G6.35	50	FT	Xenon Bi-Pin GY6.35 12V, Frosted Bulb
	EBUX-10W-G4-CL-12V	X	G4	10	CL	Xenon Bi-Pin G4 12V, Clear Bulb
	EBUX-10W-G4-FT-12V	X	G4	10	FT	Xenon Bi-Pin G4 12V, Frosted Bulb
	EBUX-25W-G9-CL-120V	X	G9	25	CL	Xenon Bi-Pin G9 120V, Clear Bulb
	EBUX-25W-G9-FT-120V	X	G9	25	FT	Xenon Bi-Pin G9 120V, Frosted Bulb
	EBUX-40W-G9-CL-120V	X	G9	40	CL	Xenon Bi-Pin G9 120V, Clear Bulb
	EBUX-40W-G9-FT-120V	X	G9	40	FT	Xenon Bi-Pin G9 120V, Frosted Bulb
	EBUX-50W-G9-CL-120V	X	G9	50	CL	Xenon Bi-Pin G9 120V, Clear Bulb
	EBUX-50W-G9-FT-120V	X	G9	50	FT	Xenon Bi-Pin G9 120V, Frosted Bulb
	EBUX-60W-G9-CL-120V	X	G9	60	CL	Xenon Bi-Pin G9 120V, Clear Bulb
	EBUX-60W-G9-FT-120V	X	G9	60	FT	Xenon Bi-Pin G9 120V, Frosted Bulb
	EBUX-75W-G9-CL-120V	X	G9	75	CL	Xenon Bi-Pin G9 120V, Clear Bulb
	EBUX-75W-G9-FT-120V	X	G9	75	FT	Xenon Bi-Pin G9 120V, Frosted Bulb

Bulb Type Glossary

CF- Compact Fluorescent

F-Fluorescent

H-Halogen

I - Incandescent

L - LED

X - Xenon

REPLACEMENT BULBS

Type	Base	Watts	Item	Description	Pervious Bulb
Compact Fluorescent	G24q-1	13W	EBUCF-CFQ13-G24Q-1-827	CFL Quad 4 Pin G24q-1 Bulb, 2700K	EBUFPL13038
Compact Fluorescent	GX23-2	13W	EBUCF-CFQ13-GX23-2-827	CFL Quad Bi-Pin GX23-2 Bulb, 2700K	EBUFPL13062
Compact Fluorescent	G24q-2	18W	EBUCF-CFQ18-G24Q-2-827	CFL Quad 4 Pin G24q-2 Bulb, 2700K	EBUFPL18039
Compact Fluorescent	2G11	18W	EBUCF-FT18-2G11-827	CFL Twin 4 Pin 2G11 Bulb, 2700K	EBUFPL18037
Compact Fluorescent	2G11	18W	EBUCF-FT18-2G11-830	CFL Twin 4 Pin 2G11 Bulb, 3000K	
Compact Fluorescent	2G11	36W	EBUCF-FT36-2G11-830	CFL Twin 4 Pin 2G11 Bulb, 3000K	
Fluorescent	T5	21W	EBUF-F21T5-827	FL T5 Linear Mini Bi-Pin Bulb, 2700K 34"L	EBUFT521014
Fluorescent	T5	21W	EBUF-F21T5-830	FL T5 Linear Mini Bi-Pin Bulb, 3000K 34"L	
Fluorescent	T5	24W	EBUF-F24T5-835	FL T5 Linear Mini Bi-Pin Bulb, 3500K 22"L	EBUFT524064
Fluorescent	T5	39W	EBUF-F39T5-835	FL T5 Linear Mini Bi-Pin Bulb, 3500K 34"L	EBUFT539065
Fluorescent	GU24	13W	EBUF-SP13-GU24-827	FL Spiral GU24 Bulb, 2700K	EBUFPL13004
Fluorescent	GU24	18W	EBUF-SP18-GU24-827	FL Spiral GU24 Bulb, 2700K	
Fluorescent	GU24	13W	EBUF-SPLP13-GU24-827	FL Low Profile Spiral GU24 Bulb, 2700K	EBUFPL13026
Fluorescent	GU24	18W	EBUF-SPLP18-GU24-827	FL Low Profile Spiral GU24 Bulb, 2700K	EBUFPL18005
Halogen	GU10	35W	EBUH-35W-GU10-CL-120V	Halogen GU10 110-130V, Clear Bulb	EBUH35050
Halogen	GU10	50W	EBUH-50W-GU10-CL-120V	Halogen GU10 110-130V, Clear Bulb	EBUH50051
Halogen	PAR20	50W	EBUH-50W-PAR20-FL-CL-120V	Halogen PAR20, 120V, Clear Bulb	EBUH50057
Incandescent	MB	60W	EBUI-60W-T10-E26-IF-120V	Incandescent MB T10 120V, Inside Frost Bulb	EBUI60029
LED	G3	.2W	EBUL-.2W-G3-CL-12V	LED G3, 3500K 12V, Clear Bulb	EBUL06074
LED	G4	1.5W	EBUL-1.5W-G4-CL-12V	LED G4, 3000K 12V, Clear Bulb (See Restriction Supp Des)	EBUL01073
LED	G9	2.9W	EBUL-2.9W-G9-CL-120V	LED G9 3500K 120V, Clear Bulb	EBUL03075
LED	G9	2.9W	EBUL-2.9W-G9-CL-120V-827	LED G9 2700K 120V, Clear Bulb	
LED	MR11	3W	EBUL-3W-MR11-CL-12V	LED MR11 3000K 12V, Clear Bulb	EBUL03070
LED	MR16	3W	EBUL-3W-MR16-FL-CL-12V	LED MR16 3000K 12V, Clear Bulb	EBUL03071
Xenon	G4	20W	EBUX-20W-G4-CL-12V	Xenon Bi-Pin G4 12V, Clear Bulb	EBUX20047
Xenon	G4	20W	EBUX-20W-G4-FT-12V	Xenon Bi-Pin G4 12V, Frosted Bulb	
Xenon	G4	35W	EBUX-35W-G4-CL-12V	Xenon Bi-Pin G4 12V, Clear Bulb	EBUX35066
Xenon	G6	35W	EBUX-35W-G6.35-CL-12V	Xenon Bi-Pin G6.35 12V, Clear Bulb	EBUX35071
Xenon	G6.35	35W	EBUX-35W-G6.35-FT-12V	Xenon Bi-Pin G6.35 12V, Frosted Bulb	
Xenon	G6.35	50W	EBUX-50W-G6.35-CL-12V	Xenon Bi-Pin G6.35 12V, Clear Bulb	EBUX50059
Xenon	G6.35	50W	EBUX-50W-G6.35-FT-12V	Xenon Bi-Pin G6.35 12V, Frosted Bulbs	
Xenon	G4	10W	EBUX-10W-G4-CL-12V	Xenon Bi-Pin G4 12V, Clear Bulb	EBUX10045
Xenon	G4	10W	EBUX-10W-G4-FT-12V	Xenon Bi-Pin G4 12V, Frosted Bulb	EBUX10046
Xenon	G9	25W	EBUX-25W-G9-CL-120V	Xenon Bi-Pin G9 120V, Clear Bulb	EBUX25031
Xenon	G9	25W	EBUX-25W-G9-FT-120V	Xenon Bi-Pin G9 120V, Frosted Bulb	
Xenon	G9	40W	EBUX-40W-G9-CL-120V	Xenon Bi-Pin G9 120V, Clear Bulb	EBUX40032
Xenon	G9	40W	EBUX-40W-G9-FT-120V	Xenon Bi-Pin G9 120V, Frosted Bulbs	EBUX40024
Xenon	G9	50W	EBUX-50W-G9-CL-120V	Xenon Bi-Pin G9 120V, Clear Bulbs	EBUX50033
Xenon	G9	50W	EBUX-50W-G9-FT-120V	Xenon Bi-Pin G9 120V, Frosted Bulbs	EBUX50042
Xenon	G9	60W	EBUX-60W-G9-CL-120V	Xenon Bi-Pin G9 120V, Clear Bulbs	EBUX60034
Xenon	G9	60W	EBUX-60W-G9-FT-120V	Xenon Bi-Pin G9 120V, Frosted Bulbs	EBUX60028
Xenon	G9	75W	EBUX-75W-G9-CL-120V	Xenon Bi-Pin G9 120V, Clear Bulbs	EBUX75058
Xenon	G9	75W	EBUX-75W-G9-FT-120V	Xenon Bi-Pin G9 120V, Frosted Bulbs	EBUX75035

Warranty and Other Information

- For specific and detailed warranty information, ask your ET2 Contemporary Lighting sales representative or visit www.et2online.com/warranty.
- ET2 Contemporary Lighting reserves the right to change details of design, materials, colors and finishes. Color may vary from what is pictured due to limitations inherent to the photographic process.
- Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do installations. Always install to a mechanically sound structure.
- Products in this supplement are UL or ETL certified. All electrical products are certified and listed to standards for use in the United States of America or Canada.
- Lamps are not included unless otherwise noted.
- Printed in China



ET2 Contemporary Lighting is a trademark of Maxim Lighting International, Inc.

StarStrand and CounterMax are registered trademarks of Maxim Lighting International, Inc.

All designs, logos, products and images © Copyright 2015 ET2 Contemporary Lighting.

All Rights Reserved.



facebook.com/et2lighting



follow us [@et2lighting](https://twitter.com/et2lighting)

LETCAT1506
\$5.00

#ET2lighting



Scan here to learn more about ET2 Contemporary Lighting

Stay Connected with us on



ET2 Contemporary Lighting

253 North Vineland Avenue
City of Industry, California
91746
USA

General Info: 626.956.4200
Customer Service: 800.486.2946
General Fax: 800.486.7337

Dallas Trade Mart: 214.748.8455
Showroom: 3901
Email: info@et2online.com
Web: www.et2online.com