

# LIGHTING CATALOG

LIGHT FIXTURES, CEILING FANS & ACCESSORIES







# CONTENTS



## INTRODUCTION 4-5

LEADING THE WAY ..... 4-5

- Our Company ..... 4
- Our Commitment..... 4
- Our Products..... 5
- Our People..... 5

## LIGHT FIXTURES 8-97

Indoor LED Light Fixtures ..... 8-13

- Boswell Collection ..... 10
- Cava Collection ..... 9
- Ceiling Light Assortment ..... 12
- Shop Lights ..... 13
- Surface Mount (Wet Location) ..... 11
- Surface Mount ..... 13

Indoor Light Fixture Collections... 14-31

- Alexander ..... 19
- Brixton ..... 16
- Callan ..... 25
- Dunmore ..... 26-27
- Elvaston ..... 24
- Ewing ..... 21
- Hansen ..... 20
- Harwell ..... 28-29
- Ingram ..... 19
- Iron Hill ..... 15
- Isadora ..... 16
- Karah ..... 23
- Lenola ..... 24
- Malvern ..... 17
- Midori ..... 18
- Montrose ..... 19
- Pacific Falls ..... 25
- Packard ..... 31
- Parker Mews ..... 30
- Ramsgate ..... 18

## LIGHT FIXTURES 8-97

- Scholar ..... 17
- Stella Mira ..... 16
- Sylvestre ..... 30
- Trinity I & II ..... 31
- Wilkes..... 22

Indoor Ceiling..... 32-43

Indoor Wall ..... 44-53

Indoor Hanging ..... 54-69

Designer You® Assortment..... 70-81

- Retro Pendants and Shades ..... 70-71
- Adjustable Pendant Fixtures..... 72-73
- Wall Fixtures ..... 74-75
- 2¼" Fitter Pendant/Vanity Glass ... 76-80
- Shelf Displays ..... 81

Outdoor..... 82-96

Light Fixture Shelf Display..... 95

Accent Lighting ..... 97

- Picture Lights ..... 97

Lamps are not included with product unless otherwise noted. We recommend using Westinghouse lamps in all of our ceiling fans and light fixtures. Westinghouse Lighting reserves the right to make changes and/or improvements (both visually and technically) to the products in this catalog without notice. As a result, some products and/or product information may change.

Visit our website for the latest specifications.



# Westinghouse

INNOVATION YOU CAN BE SURE OF

# CONTENTS



**CEILING FANS 98-145**

Contemporary .....102-121

    Aerialist ..... 112

    Alloy .....109

    Alloy LED.....108

    Alloy II .....108

    Alta Vista .....106

    Arcadia..... 115

    Bendan .....111

    Bendan LED ..... 111

    Bocca ..... 111

    Bolton.....105

    Castle .....106

    Castle LED.....106

    Cayuga.....104

    Comet.....107

    Cumulus ..... 114

    Delancey ..... 110

    Delancey LED ..... 110

    Desoto .....105

    Elite ..... 116

    Harmony..... 113

    Lavada ..... 114

    Origami ..... 121

    Panorama..... 117

    Quince ..... 121

    Roundabout ..... 118

    Solana..... 113

    Sparta..... 113

    Techno .....103

    Techno II.....103

    Troy ..... 110

    Turbo Swirl..... 119

    Turbo Swirl CFL ..... 118

    Turbo Swirl LED ..... 118

    Vector Elite ..... 116

    Wengue .....120

    Xavier ..... 117

    Xavier II..... 117

    Zander .....107

    Zephyr .....105

**CEILING FANS 98-145**

Traditional ..... 122-135

    Aiden..... 123

    Anderson..... 125

    Bethany .....93

    Carolina LED..... 129

    Casanova .....134

    Casanova Supreme ..... 134

    Cassidy ..... 129

    Contempra IV .....130-131

    Contempra Trio..... 132-133

    Fairview ..... 125

    Goodwin..... 128

    Hadley..... 132

    Newtown ..... 128

    Petite..... 135

    Richboro SE..... 128

    Sumter LED.....130

    Swirl..... 126

    Thurlow ..... 123

    Tulsa ..... 124

    Tulsa LED..... 124

    Vintage..... 127

    Vintage II ..... 126

Outdoor..... 136-139

    Brentford ..... 137

    Comet..... 139

    Great Falls ..... 137

    Lafayette ..... 138

    Lafayette LED..... 138

    Oasis ..... 139

Industrial & Contractor ..... 140-142

    Contractor's Choice..... 142

    Industrial .....141-142

    Urban Gale..... 141

Ceiling Fan Specifications -  
Dimensions ..... 143

Ceiling Fan Specifications ..... 144-145



**CEILING FAN ACCESSORIES 146-155**

Ceiling Fan LED Light Kits ..... 147  
 Cathedral Ceiling Fan Canopy Kits ..... 148  
 Extension Down Rods ..... 148  
 Ceiling Fan Controls ..... 149  
 Pull Chains ..... 150-152  
 All-Purpose Dusters ..... 152  
 Fan Blade Arms, Replacement Blades & Canopy Kits ..... 153  
 Beaded Chain, Connectors & Hardware .. 154  
 Fan Switches ..... 155



**CEILING FAN & LIGHT FIXTURE ACCESSORIES 156-169**

Recessed Light Converter ..... 157  
 Ceiling Medallions ..... 158-160  
     Medallion Size & Installation Guide .... 158  
     Polyurethane Medallions ..... 159  
     Molded Plastic Medallions ..... 160  
 Support Braces & Boxes for Ceiling Fans & Light Fixtures... 161-169  
     Saf-T-Brace® ..... 161-163  
     Saf-T-Bar® ..... 164  
     Saf-T-Box® ..... 165  
     Sidemount Plus Fan Box® ..... 166  
     Saf-T-Pan® ..... 167  
     Fan Master Jr.® & Fan Master® ..... 168  
     Saf-T-Grid® ..... 169



**REPLACEMENT GLASSWARE & ASSORTED SHADES 170-186**

2 1/4" Fitters ..... 171-178  
 Chimneys ..... 179  
 Glass Diffusers ..... 180-181  
 Globes 3 1/4" & 4" Fitters ..... 182  
 Polycarbonate & Acrylic Shades ..... 183  
 Assorted Shades, Fitters & Channels ..... 184  
 Clip-On Shades ..... 185  
 Glassware Glossary ..... 186  
 Plastic Material Guide ..... 186

**LIGHTING HARDWARE BULK & PACKAGED 187-218**

Glass Shade Holders & Accessories ..... 188  
 Sockets ..... 189-195  
 Socket Reducers & Shade Rings ..... 195  
 Specialty Sockets & Lamp Holders... 196-197  
 Switches ..... 198-199  
 Crossbars ..... 200-201  
 Nipples & All-Thread Pipes ..... 202  
 Assorted Hardware ..... 203-204  
 Beaded Chain & Connectors ..... 205  
 Canopies & Blank-Up Kits ..... 206-207  
 Swag Light Kits, Chain & Swag Hook Kits ..... 208-209  
 Make-A-Lamp Kits ..... 210  
 Harps ..... 211  
 Finials & Knobs ..... 212-213  
 Parts & Accessories ..... 214-215  
 Plugs ..... 216  
 Accessories ..... 217-218

**INDEX 219-224**

# LEADING THE WAY



## *Our Company*

Westinghouse Lighting is a well-recognized global brand and a market leader in the lighting fixture and ceiling fan industries. Known for innovative products of the highest quality, we continue to expand our product offering year after year.

## *Our Commitment*

For over 70 years, dedication to customer relationships has consistently been our greatest priority at Westinghouse Lighting. We have built and maintained a solid reputation for quality products, timely shipments and friendly service.



# QUALITY, INNOVATION & COMMITMENT



## Our Products

We offer a wide assortment of indoor and outdoor lighting fixtures and ceiling fans, ranging from traditional to contemporary. Our decorative glassware and shade collection offers stylish options for any décor, while our selection of replacement glassware, lamp parts and ceiling fan accessories helps with any repair or replacement need.



## Our People

Our knowledgeable, experienced and passionate team of people has been the cornerstone in our continued success and growth throughout the years. We stand ready to offer support and long term solutions for all of your lighting needs.



# LIGHT FIXTURES



## *LED Indoor Fixtures*

Westinghouse LED fixtures offer something for every design style, from modern to traditional. Energy-efficient and long-lasting, LED lighting fixtures provide savings and convenience.



## *Hanging / Pendant Fixtures*

A room's focal point is often an exquisite chandelier or statement-making pendant. From contemporary to traditional, our diverse assortment of styles will add simple elegance to any room.



All light fixtures in this catalog are Underwriter Laboratories or ETL Listed for safety. All Westinghouse light fixtures are warranted against defects in material and workmanship for a period of five years from their purchase date.



## Ceiling / Wall Fixtures

Bring new life and light to any space with our wide range of attractive ceiling and wall fixtures. Available in styles and sizes that will accentuate, illuminate and complement any décor.



## Outdoor Fixtures



WET LOCATION RATED

Lighting fixtures add security, personality, and a warm, welcoming touch outside a home. The timeless designs of Westinghouse outdoor lighting fixtures can change any home from ordinary to extraordinary.

Look for these symbols to indicate important energy-saving features for light fixtures.



Integrated Dimmable LED



Integrated LED



Dimmable LED Lamps



Non-Dimmable LED Lamps





## INDOOR LED FIXTURES

From practical shop lights to fashionable pendants, Westinghouse offers LED fixtures for your everyday lighting needs. These fixtures are long-lasting and provide significant energy savings to reduce your carbon footprint.



# Cava Collection

Dazzling bubble glass creates a uniquely modern look.



INTEGRATED  
DIMMABLE  
LED

**\*63076**  
**1 Light LED Wall**  
Chrome Finish with Bubble Glass  
Height: 7.76" Width: 4.96"  
Extends: 5.69"  
Includes 8 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**\*63077**  
**2 Light LED Wall**  
Chrome Finish with Bubble Glass  
Height: 7.76" Width: 9.46" Extends: 5.69"  
Includes 2 x 7.5 Watt Integrated LEDs



INTEGRATED  
DIMMABLE  
LED

**\*63119**  
**3 Light LED Wall**  
Chrome Finish with Bubble Glass  
Height: 7.76" Width: 15.16" Extends: 5.69"  
Includes 3 x 7.33 Watt Integrated LEDs



INTEGRATED  
DIMMABLE  
LED



Bubble Glass  
Detail Shown

**63079**  
**1 Light LED Mini Pendant**  
Chrome Finish with Bubble Glass  
Height: 61.05"  
Diameter: 4.96"  
Adjustable Cord: 50"  
Includes 8 Watt Integrated LED



INTEGRATED  
LED

**64010**  
**1 Light LED Pendant**  
Black Finish with Chrome Cage  
Height: 61.5"  
Diameter: 12.13"  
Adjustable Cord: 50"  
Includes 13 Watt Integrated LED

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
63076	*	8	40	3000 (Warm White)	360	80	25000	22.8	\$0.96
63077	*	15	80 (2 x 40)	3000 (Warm White)	730	80	25000	22.8	\$1.81
63119	*	22	120 (3 x 40)	3000 (Warm White)	1300	80	25000	22.8	\$2.65
63079	*	8	40	3000 (Warm White)	450	80	25000	22.8	\$0.96
64010	*	16	75	3000 (Warm White)	900	80	30000	27.3	\$1.93

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).  
\* Integrated LED Light Source

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

\*Fixture can be installed up or down

# Boswell Collection

Industrial vintage style in a variety of trending finishes. Choose your size, choose your wattage.



**DIMMABLE  
LED**

**1 Light LED Mini Pendant**  
Oil Rubbed Bronze Finish  
with Highlights and Prismatic Lens  
Height: 41.34" Diameter: 8.75"

**63082A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63082B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE  
LED**

**1 Light LED Mini Pendant**  
Chrome Finish  
with Prismatic Lens  
Height: 41.34" Diameter: 8.75"

▲ **63083A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63083B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE  
LED**

**1 Light LED Mini Pendant**  
Washed Copper Finish  
with Prismatic Lens  
Height: 41.34" Diameter: 8.75"

**63084A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63084B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE  
LED**

**1 Light LED Pendant**  
Oil Rubbed Bronze Finish  
with Highlights and Prismatic Lens  
Height: 43.54" Diameter: 10.63"

▲ **63087A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63087B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE  
LED**

**1 Light LED Pendant**  
Chrome Finish  
with Prismatic Lens  
Height: 43.54" Diameter: 10.63"

**63085A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63085B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE  
LED**

**1 Light LED Pendant**  
Washed Copper Finish  
with Prismatic Lens  
Height: 43.54" Diameter: 10.63"

▲ **63086A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63086B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp

Boswell Collection includes (3) 9.5" long rods. Install 1, 2, or 3 rods for customized lengths.

## DIMMABLE LED LIGHT SOURCE SPECIFICATIONS

Model Type	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Avg. Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
Model A	1	9	60	3000 (Warm White)	800	80	25000	22.8	\$1.08
Model B	1	11	75	3000 (Warm White)	1100	80	25000	22.8	\$1.32

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

▲ Design Collection

# SURFACE MOUNT FIXTURES



**Small LED Surface Mount**  
 Chrome Finish with Frosted Lens  
 Height: 1" Diameter: 6"  
 Includes 12 Watt Integrated LED  
**63218** - 3000K  
**63222** - 4000K



**Large LED Surface Mount**  
 Chrome Finish with Frosted Lens  
 Height: 1.37" Diameter: 7.38"  
 Includes 15 Watt Integrated LED  
**63226** - 3000K  
**63230** - 4000K



**Small LED Surface Mount**  
 Brushed Nickel Finish with Frosted Lens  
 Height: 1" Diameter: 6"  
 Includes 12 Watt Integrated LED  
**63219** - 3000K  
**63223** - 4000K



**Large LED Surface Mount**  
 Brushed Nickel Finish with Frosted Lens  
 Height: 1.37" Diameter: 7.38"  
 Includes 15 Watt Integrated LED  
**63227** - 3000K  
**63231** - 4000K



**Small LED Surface Mount**  
 Oil Rubbed Bronze Finish with Frosted Lens  
 Height: 1" Diameter: 6"  
 Includes 12 Watt Integrated LED  
**63220** - 3000K  
**63224** - 4000K



**Large LED Surface Mount**  
 Oil Rubbed Bronze Finish with Frosted Lens  
 Height: 1.37" Diameter: 7.38"  
 Includes 15 Watt Integrated LED  
**63228** - 3000K  
**63232** - 4000K



**Small LED Surface Mount**  
 White Finish with Frosted Lens  
 Height: 1" Diameter: 6"  
 Includes 12 Watt Integrated LED  
**63221** - 3000K  
**63225** - 4000K



**Large LED Surface Mount**  
 White Finish with Frosted Lens  
 Height: 1.37" Diameter: 7.38"  
 Includes 15 Watt Integrated LED  
**63229** - 3000K  
**63233** - 4000K

## DIMMABLE LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Avg. Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
63218	*	12	60	3000 (Warm White)	840	80	50000	45.6	\$1.45
63222	*	12	60	4000 (Warm White)	840	80	50000	45.6	\$1.45
63219	*	12	60	3000 (Warm White)	840	80	50000	45.6	\$1.45
63223	*	12	60	4000 (Warm White)	840	80	50000	45.6	\$1.45
63220	*	12	60	3000 (Warm White)	840	80	50000	45.6	\$1.45
63224	*	12	60	4000 (Warm White)	840	80	50000	45.6	\$1.45
63221	*	12	60	3000 (Warm White)	840	80	50000	45.6	\$1.45
63225	*	12	60	4000 (Warm White)	840	80	50000	45.6	\$1.45
63226	*	15	75	3000 (Warm White)	1050	80	50000	45.6	\$1.81
63230	*	15	75	4000 (Warm White)	1050	80	50000	45.6	\$1.81
63227	*	15	75	3000 (Warm White)	1050	80	50000	45.6	\$1.81
63231	*	15	75	4000 (Warm White)	1050	80	50000	45.6	\$1.81
63228	*	15	75	3000 (Warm White)	1050	80	50000	45.6	\$1.81
63232	*	15	75	4000 (Warm White)	1050	80	50000	45.6	\$1.81
63229	*	15	75	3000 (Warm White)	1050	80	50000	45.6	\$1.81
63233	*	15	75	4000 (Warm White)	1050	80	50000	45.6	\$1.81

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

\* Integrated LED Light Source

# CEILING LIGHT FIXTURE ASSORTMENT

**63088**

**11" LED Flush**

Brushed Nickel Finish  
with White Alabaster Glass

Height: 3.46" Diameter: 11"

Includes 16 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**63089**

**11" LED Flush**

Oil Rubbed Bronze Finish  
with White Alabaster Glass

Height: 3.46" Diameter: 11"

Includes 16 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED



INTEGRATED  
DIMMABLE  
LED

**64005**

**11" LED Flush**

Brushed Nickel Finish  
with White Alabaster Glass

Height: 4.75" Diameter: 11"

Includes 15 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64012**

**15 3/4" LED Flush**

Brushed Nickel Finish  
with White Acrylic Shade

Height: 3.50" Diameter: 15.75"

Includes 23 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64009**

**11 7/8" LED Semi-Flush**

Brushed Nickel Finish  
with White Acrylic Shade

Height: 9.50" Diameter: 11.88"

Includes 15 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64006**

**11" LED Flush**

Oil Rubbed Bronze Finish  
with White Alabaster Glass

Height: 4.75" Diameter: 11"

Includes 15 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64007**

**11" LED Flush**

Oil Rubbed Bronze Finish  
with White Alabaster Glass

Height: 4.63" Diameter: 11"

Includes 14.5 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64008**

**11" LED Flush**

Oil Rubbed Bronze Finish  
with White Alabaster Glass

Height: 4.63" Diameter: 11"

Includes 12 Watt Integrated LED

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
63088	*	16	75	3000 (Warm White)	1000	80	30000	27.3	\$1.93
63089	*	16	75	3000 (Warm White)	1000	80	30000	27.3	\$1.93
64005	*	15	60	3000 (Warm White)	930	80	30000	27.3	\$1.75
64012	*	23	100	3000 (Warm White)	1600	80	30000	27.3	\$2.77
64009	*	15	75	3000 (Warm White)	1000	80	30000	27.3	\$1.81
64006	*	15	60	3000 (Warm White)	930	80	30000	27.3	\$1.81
64007	*	14.5	60	3000 (Warm White)	930	80	30000	27.3	\$1.75
64008	*	12	40	3000 (Warm White)	730	80	30000	27.3	\$1.45

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

\* Integrated LED Light Source

# SURFACE MOUNT FIXTURES



**INTEGRATED DIMMABLE LED**

**62049**  
**8 7/8" LED Round Flush**  
 White Finish with Frosted Polycarbonate Panel  
 Height: 1.50" Diameter: 8.86"  
 Includes 14 Watt Integrated LED



**INTEGRATED DIMMABLE LED**

**62050**  
**8 7/8" LED Square Flush**  
 White Finish with Frosted Polycarbonate Panel  
 Height: 1.50" Square: 8.86"  
 Includes 14 Watt Integrated LED



**INTEGRATED LED**

**64011**  
**11" LED Flush**  
 White Finish with White Acrylic Shade  
 Height: 3.50" Diameter: 11"  
 Includes 15 Watt Integrated LED


# SHOP LIGHTS

- Durable, lightweight design includes convenient 12" adjustable hanging chains.
- 5 ft. 3-prong, plug-in cord offers versatility and the on/off pull chain provides convenient control - no wiring needed.
- Impact-resistant frosted polycarbonate lens provides glare-free light.
- 48" fixture (#63217) includes convenient linking cord to connect up to 5 fixtures.



**INTEGRATED LED**

**63216**  
**36" LED Shop Light**  
 Silver Finish with Frosted Lens  
 Height: 2.80" Diameter: 2.80"  
 Chain: 12" Cord: 60"  
 Includes 38 Watt Integrated LED



**14" Linking Cord**

Item #63217 includes convenient linking cord to connect up to 5 fixtures.



**INTEGRATED LED**

**63217**  
**48" LED Shop Light**  
 Silver Finish with Frosted Lens  
 Height: 2.80" Diameter: 2.80"  
 Chain: 12" Cord: 60"  
 Includes 48 Watt Integrated LED

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
62049	*	14	60	3000 (Warm White)	800	80	30000	27.3	\$1.69
62050	*	14	60	3000 (Warm White)	800	80	30000	27.3	\$1.69
64011	*	15	75	3000 (Warm White)	1000	80	30000	27.3	\$1.81
63216	*	38	N/A	4000 (Warm White)	3000	80	50000	45.6	\$4.58
63217	*	48	N/A	4000 (Warm White)	4000	80	50000	45.6	\$5.78

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

\* Integrated LED Light Source





## INDOOR LIGHT FIXTURE COLLECTIONS

Every aspect of a room reflects style. From a master bedroom to a kitchen island, from a dining room to a two-story foyer, Westinghouse offers a collection of light fixtures in styles that will complement any space.

# Iron Hill Collection

Industrial, vintage style is perfect for any décor from modern spaces to farmhouse kitchens.



**63447**  
**1 Light Pendant**  
 Oil Rubbed Bronze Finish with Highlights and Metallic Bronze Interior  
 Height: 57.15" Diameter: 12"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63449**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish with Highlights and Metallic Bronze Interior  
 Height: 7.38" Width: 29.09" Extends: 9.65"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**63448**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish with Highlights and Metallic Bronze Interior  
 Height: 7.9" Width: 8.67"  
 Extends: 9.65"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63450**  
**4 Light Chandelier/Semi-Flush**  
 Oil Rubbed Bronze Finish with Highlights and Metallic Bronze Interior  
 Height: 16.34" Diameter: 25.16"  
 Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**63434**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish with Highlights  
 Height: 7.38" Width: 29.09" Extends: 9.65"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**63435**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish with Highlights  
 Height: 7.90" Width: 8.67"  
 Extends: 9.65"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63433**  
**4 Light Chandelier/Semi-Flush**  
 Oil Rubbed Bronze Finish with Highlights  
 Height: 16.34" Diameter: 25.16" Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**Westinghouse**  
**VINTAGE LAMPS**

Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.

Height shown for Iron Hill fixtures is without lamps.

\*Fixture can be Chandelier or Semi-Flush Mount

## Isadora Collection

Remarkable craftsmanship elevates this elegant, open cylinder design.



Highlight  
Detail Shown

**63037**

### 3 Light Chandelier

Oil Rubbed Bronze Finish  
with Highlights

Height: 18.75" Diameter: 12.75"

Chain: 36" Cord: 60"

Use (3) Candelabra

(E12) Base Lamps,  
40 Watt Maximum



**63038**

### 3 Light Chandelier

Brushed Nickel Finish

Height: 18.75" Diameter: 12.75"

Chain: 36" Cord: 60"

Use (3) Candelabra

(E12) Base Lamps,  
40 Watt Maximum



## Stella Mira Collection

Industrial undertones radiate from an open sphere design.

**63419**

### 3 Light Pendant

Brushed Nickel Finish

Height: 17.28"

Diameter: 15.04"

Chain: 36" Cord: 60"

Use (3) Candelabra (E12)

Base Lamps, 40 Watt Maximum



**63418**

### 3 Light Pendant

Oil Rubbed Bronze Finish  
with Highlights

Height: 17.28"

Diameter: 15.04"

Chain: 36" Cord: 60"

Use (3) Candelabra (E12)

Base Lamps, 40 Watt Maximum



## Brixton Collection

Elegant, sophisticated open sphere design.

**63033**

### 6 Light Chandelier

Oil Rubbed Bronze Finish with Highlights

Height: 18.03" Diameter: 25"

Chain: 36" Cord: 60"

Use (6) Candelabra (E12)

Base Lamps, 40 Watt Maximum



Highlight  
Detail Shown



**63031**

### 6 Light Chandelier

Brushed Nickel Finish

Height: 18.03" Diameter: 25"

Chain: 36" Cord: 60"

Use (6) Candelabra (E12)

Base Lamps, 40 Watt Maximum



Add Westinghouse  
Filament LED or Timeless lamps  
for the vintage look you want.

 Westinghouse  
VINTAGE LAMPS





# Scholar Collection

Traditional, vintage design is refined to fit today's trendy styles.



**63422**  
**1 Light Semi-Flush**  
 Oil Rubbed Bronze Finish  
 with White Opal Glass  
 Height: 9.06" Diameter: 7.36"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**63421**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish with White Opal Glass  
 Height: 9.96" Width: 24.02" Extends: 7.99"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**63420**  
**4 Light Chandelier/Semi-Flush**  
 Oil Rubbed Bronze Finish with White Opal Glass  
 Height: 20.08" Diameter: 23.86" Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



# Malvern Collection

Rich bronze highlights and detailed smoldering scavo glass exude warmth and add sophistication.



**\*63021**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Smoldering Scavo Glass  
 Height: 12.36" Width: 5.12"  
 Extends: 7.17"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**\*63022**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Smoldering Scavo Glass  
 Height: 11.85" Width: 19.69"  
 Extends: 8.74"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**81017**  
**Smoldering Scavo  
 Cone Shade**  
 Fitter: 2.25"  
 Height: 5.60"  
 Diameter: 4.75"

**63023**  
**2 Light Flush**  
 Oil Rubbed Bronze Finish  
 with Smoldering Scavo Glass  
 Height: 6.85" Diameter: 12.99"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**63071**  
**5 Light Chandelier**  
 Oil Rubbed Bronze Finish  
 with Smoldering Scavo Glass  
 Height: 23.03" Diameter: 24.09" Chain: 36" Cord: 60"  
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum

\*Fixture can be installed up or down  
 †Fixture can be Chandelier or Semi-Flush Mount

# Ramsgate Collection

Glistening ice glass and strong swooping arms make a statement.



**\* 63025**  
**1 Light Wall**  
 Brushed Nickel Finish with Ice Glass  
 Height: 9" Width: 5.12" Extends: 7.50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**\* 63026**  
**2 Light Wall**  
 Brushed Nickel Finish with Ice Glass  
 Height: 9" Width: 12" Extends: 6.50"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**\* 63081**  
**3 Light Wall**  
 Brushed Nickel Finish with Ice Glass  
 Height: 9" Width: 20" Extends: 7.50"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\* 85006**  
**Ice Cylinder Shade**  
 Fitter: 2.25"  
 Height: 5.15"  
 Diameter: 4"

**63080**  
**5 Light Chandelier**  
 Brushed Nickel Finish with Ice Glass  
 Height: 22" Diameter: 24" Chain: 36" Cord: 60"  
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum

# Midori Collection

Amber linen glass brings warmth to this graceful family with global style.



**\* 63074**  
**2 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Amber Linen Glass  
 Height: 10.71" Width: 14.96" Extends: 7.09"  
 Use (2) Medium (E26)  
 Base Lamps, 60 Watt Maximum



**\* 63075**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Amber Linen Glass  
 Height: 10.12" Width: 20.87" Extends: 7.09"  
 Use (3) Medium (E26)  
 Base Lamps, 60 Watt Maximum



**\* 81009**  
**Amber Linen Flared Cube Shade**  
 Fitter: 2.25"  
 Height: 5.27"  
 Width: 5"



**63030**  
**2 Light Flush**  
 Oil Rubbed Bronze Finish  
 with Amber Linen Glass  
 Height: 6.57" Diameter: 12.99"  
 Use (2) Medium (E26)  
 Base Lamps, 60 Watt Maximum



**\* 63073**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Amber Linen Glass  
 Height: 8.54" Width: 5.12" Extends: 7.09"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**63072**  
**5 Light Chandelier**  
 Oil Rubbed Bronze Finish with Amber Linen Glass  
 Height: 27.72" Diameter: 23.82"  
 Chain: 36" Cord: 60"  
 Use (5) Medium (E26) Base Lamps,  
 60 Watt Maximum

•Hand Blown Glass  
 \*Fixture can be installed up or down

# Montrose Collection

Rich bronze highlights and detailed scavo glass exude warmth and add sophistication.



**\*63428**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Highlights and Mocha Scavo Glass  
 Height: 10.67" Width: 19" Extends: 8.50"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\*81005**  
**Mocha Scavo Bell with Raised Band**  
 Fitter: 2.25"  
 Height: 5.70"  
 Diameter: 5"



**63429**  
**5 Light Chandelier**  
 Oil Rubbed Bronze Finish with  
 Highlights and Mocha Scavo Glass  
 Height: 27.44" Diameter: 23.50" Chain: 36" Cord: 60"  
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



**63432**  
**2 Light Flush**  
 Oil Rubbed Bronze Finish  
 with Highlights and Mocha Scavo Glass  
 Height: 6.81" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**63431**  
**1 Light Mini Pendant**  
 Oil Rubbed Bronze Finish with Highlights  
 and Mocha Scavo Glass  
 Height: 40.08" Diameter: 6.38"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum  
 Includes (3) 9.5" long rods.  
 Install 1, 2, or 3 rods for customized lengths.

# Alexander Collection

Distinctively textured glass enhances clean, contemporary lines.



**\*63039**  
**2 Light Wall**  
 Brushed Nickel Finish  
 with Rippled White Glazed Glass  
 Height: 11.14" Width: 15.24"  
 Extends: 5.90"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**\*63040**  
**3 Light Wall**  
 Brushed Nickel Finish  
 with Rippled White Glazed Glass  
 Height: 11.14" Width: 22.5"  
 Extends: 5.90"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**\*63041**  
**4 Light Wall**  
 Brushed Nickel Finish  
 with Rippled White Glazed Glass  
 Height: 11.14" Width: 30.24" Extends: 5.90"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**\*85045**  
**Rippled White Glazed Rectangular Shade**  
 Fitter: 2.25"  
 Height: 6"  
 Width: 6"  
 Depth: 4"



**\*85044**  
**Wavy White Glazed Square Shade**  
 Fitter: 2.25" Height: 6"  
 Width: 3.75"

**63024**  
**4 Light Chandelier**  
 Brushed Nickel Finish  
 with Wavy White Glazed Glass  
 Height: 15.98" Diameter: 19.41"  
 Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps,  
 60 Watt Maximum

\*Hand Blown Glass  
 \*Fixture can be installed up or down

# Hansen Collection

Luminous, chrome finish accentuates classic lines for a transitional look.

**DESIGN**  
COLLECTION



**63441A**

### 5 Light Chandelier

Chrome Finish with White Linen Glass and Translucent Band

Height: 21.5" Diameter: 24.21" Chain: 36" Cord: 60"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



\* **63438A**

### 3 Light Wall

Chrome Finish with White Linen Glass and Translucent Band

Height: 7.80" Width: 19.69" Extends: 6.50"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



\* **81014**

### White Linen Cylinder Shade with Translucent Band

Fitter: 2.25"  
Height: 5.12"  
Diameter: 3.94"



**63441B**

### 5 Light Chandelier

Chrome Finish with White Linen Glass

Height: 21.50" Diameter: 24.21" Chain: 36" Cord: 60"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



\* **63438B**

### 3 Light Wall

Chrome Finish with White Linen Glass

Height: 7.80" Width: 19.69" Extends: 6.50"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



\* **81016**

### White Linen Cylinder Shade

Fitter: 2.25"  
Height: 5.12"  
Diameter: 3.94"



**63441C**

### 5 Light Chandelier

Chrome Finish with Glazed Ice Glass

Height: 21.50" Diameter: 25.28" Chain: 36" Cord: 60"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



\* **63438C**

### 3 Light Wall

Chrome Finish with Glazed Ice Glass

Height: 8.66" Width: 20.75" Extends: 7.05"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



\* **81018**

### Glazed Ice Cubic Dome

Fitter: 2.25"  
Height: 6"  
Diameter: 5"

•Hand Blown Glass

\*Fixture can be installed up or down



# Ewing Collection

Elegant design blends seamlessly with any space.

**DESIGN  
COLLECTION**



**63443A**  
**5 Light Chandelier**  
Oil Rubbed Bronze Finish with Amber Linen Glass  
Height: 21.50" Diameter: 25.35" Chain: 36" Cord: 60"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



**63408**  
**2 Light Flush**  
Oil Rubbed Bronze Finish with Amber Linen Glass  
Height: 4.25" Square: 11"  
Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63442A**  
**3 Light Wall**  
Oil Rubbed Bronze Finish with Amber Linen Glass  
Height: 7.80" Width: 20.87" Extends: 7.09"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\*81009**  
**Amber Linen Flared Cube Shade**  
Fitter: 2.25"  
Height: 5.27"  
Diameter: 5"



**63443B**  
**5 Light Chandelier**  
Oil Rubbed Bronze Finish with Amber Harvest Glass  
Height: 21.50" Diameter: 24.21" Chain: 36" Cord: 60"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63442B**  
**3 Light Wall**  
Oil Rubbed Bronze Finish with Amber Harvest Glass  
Height: 7.80" Width: 19.69" Extends: 6.50"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\*81015**  
**Amber Harvest Cylinder Shade**  
Fitter: 2.25"  
Height: 5.12"  
Diameter: 3.94"



**63443C**  
**5 Light Chandelier**  
Oil Rubbed Bronze Finish with Smoldering Scavo Glass  
Height: 21.50" Diameter: 25" Chain: 36" Cord: 60"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63442C**  
**3 Light Wall**  
Oil Rubbed Bronze Finish with Smoldering Scavo Glass  
Height: 8.31" Width: 20.47" Extends: 6.89"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**81017**  
**Smoldering Scavo Cone Shade**  
Fitter: 2.25"  
Height: 5.60"  
Diameter: 4.75"

\*Hand Blown Glass  
\*Fixture can be installed up or down



## Wilkes Collection

Clean, transitional style with an artistic flair.

DESIGN  
COLLECTION



**63436A**  
**4 Light Chandelier**  
Gun Metal Finish with Lunar Weave Glass  
Height: 15.94" Diameter: 20.04" Chain: 36" Cord: 60"  
Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**63436B**  
**4 Light Chandelier**  
Gun Metal Finish with White Linen Glass  
Height: 15.94" Diameter: 20.04" Chain: 36" Cord: 60"  
Use (4) Medium (E26) Base Lamps, 60 Watt Maximum


**63427**  
**2 Light Flush**  
Gun Metal Finish  
with Lunar Weave Glass  
Height: 4.25" Square: 11"  
Use (2) Medium (E26)  
Base Lamps, 60 Watt Maximum



**\*63437A**  
**3 Light Wall**  
Gun Metal Finish with Lunar Weave Glass  
Height: 10.35" Width: 21.85" Extends: 6.46"  
Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum



**•81006**  
**Lunar Weave  
Flair Cube Shade**  
Fitter: 2.25"  
Height: 5.27"  
Diameter: 5"



**\*63437B**  
**3 Light Wall**  
Gun Metal Finish with White Linen Glass  
Height: 10.35" Width: 21.85" Extends: 6.46"  
Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum



**•81013**  
**White Linen  
Flaired Cube Shade**  
Fitter: 2.25"  
Height: 5.27"  
Diameter: 5"

•Hand Blown Glass  
\*Fixture can be installed up or down

# Karah Collection

Two distinctive finishes provide options for an elegant or rustic style.

**63412**

**5 Light Chandelier**

Brushed Nickel Finish  
with White Linen Glass

Height: 18" Diameter: 23"

Chain: 36" Cord: 60"

Use (5) Medium (E26)

Base Lamps,

60 Watt Maximum



• **81003**

**White Linen  
Barrel Shade**

Fitter: 2.25"

Height: 5.30"

Diameter: 4.92"



**63409**

**2 Light Flush**

Brushed Nickel Finish  
with White Linen Glass

Height: 5.63" Diameter: 12"

Use (2) Medium (E26) Base Lamps,

60 Watt Maximum



**63410**

**3 Light Flush**

Brushed Nickel Finish  
with White Linen Glass

Height: 6.53" Diameter: 15"

Use (3) Medium (E26) Base Lamps,

60 Watt Maximum

\* **63415**

**3 Light Wall**

Oil Rubbed Bronze Finish  
with Aged Amber Scavo Glass

Height: 7.72" Width: 22" Extends: 7.09"

Use (3) Medium (E26) Base Lamps,

60 Watt Maximum



**63414**

**3 Light Flush**

Oil Rubbed Bronze Finish  
with Aged Amber Scavo Glass

Height: 6.53" Diameter: 15"

Use (3) Medium (E26) Base Lamps,

60 Watt Maximum



**63413**

**2 Light Flush**

Oil Rubbed Bronze Finish  
with Aged Amber Scavo Glass

Height: 5.63" Diameter: 12"

Use (2) Medium (E26) Base Lamps,

60 Watt Maximum

•Hand Blown Glass

\*Fixture can be installed up or down

# Lenola Collection

*Infinity-styled scrollwork and warm fabric shades impart traditional elegance.*



**63027**

**2 Light Wall**

*Amber Bronze Finish with Beige Fabric Shades*

*Height: 13.58" Width: 16.57" Extends: 7.87"  
Use (2) Candelabra (E12) Base Lamps, 40 Watt Maximum*



**63028**

**3 Light Wall**

*Amber Bronze Finish with Beige Fabric Shades*

*Height: 12.76" Width: 23.90" Extends: 7.87"  
Use (3) Candelabra (E12) Base Lamps, 40 Watt Maximum*



**63029**

**5 Light Chandelier**

*Amber Bronze Finish with Beige Fabric Shades*

*Height: 30.12" Diameter: 25" Chain: 36" Cord: 60"  
Use (5) Candelabra (E12) Base Lamps, 40 Watt Maximum*

# Elvaston Collection

*Complementary curved lines bring balance.*



**\* 63034**

**3 Light Wall**

*Oil Rubbed Bronze Finish with Frosted Glass*

*Height: 8.86" Width: 23.07" Extends: 7.48"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*



**85047**

**Frosted Dome Shade**

*Fitter: 2.25"  
Height: 4.69"  
Diameter: 5.79"*



**\* 63035**

**4 Light Wall**

*Oil Rubbed Bronze Finish with Frosted Glass*

*Height: 8.50" Width: 31" Extends: 7.48"  
Use (4) Medium (E26) Base Lamps, 60 Watt Maximum*



**\* 63036**

**5 Light Wall**

*Oil Rubbed Bronze Finish with Frosted Glass*

*Height: 9.25" Width: 39" Extends: 7.48"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*



**\* Fixture can be installed up or down**



# Callan Collection

Charming and traditional, decorative scrollwork creates an elegant appeal.

**63405**

**2 Light Flush**

Oil Rubbed Bronze Finish  
with Caramel Scavo Glass

Height: 6.65" Diameter: 13"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum



**\*63406**

**3 Light Wall**

Oil Rubbed Bronze Finish  
with Caramel Scavo Glass

Height: 7.75" Width: 24" Extends: 8.86"  
Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum



**63407**

**5 Light Chandelier**

Oil Rubbed Bronze Finish  
with Caramel Scavo Glass

Height: 21.06" Diameter: 22.91"  
Chain: 36" Cord: 60"  
Use (5) Medium (E26) Base Lamps,  
60 Watt Maximum



**81002**

**Caramel Scavo Bell**

Fitter: 2.25"  
Height: 4.61"  
Diameter: 6.06"



# Pacific Falls Collection

Clean, curved lines provide transitional elegance that blends beautifully with any décor.

**63400**

**2 Light Flush**

Amber Bronze Finish  
with White Alabaster Glass

Height: 6.89" Diameter: 13"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum




**63402**

**1 Light Mini Pendant**

Amber Bronze Finish  
with White Alabaster Glass

Height: 42.20" Diameter: 7"  
Use (1) Medium (E26)  
Base Lamp, 60 Watt Maximum  
Includes (3) 11.5" long rods.  
Install 1, 2, or 3 rods for  
customized lengths.



**\*63403**

**2 Light Pendant/Semi-Flush**

Amber Bronze Finish  
with White Alabaster Glass

Height: 13.86" Diameter: 13.98"  
Chain: 36" Cord: 60"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum



**63404**

**5 Light Chandelier**

Amber Bronze Finish  
with White Alabaster Glass

Height: 24" Diameter: 24.72"  
Chain: 36" Cord: 60"  
Use (5) Medium (E26)  
Base Lamps, 60 Watt Maximum



**81000**

**White Alabaster Flared Bell**

Fitter: 2.25"  
Height: 4.33"  
Diameter: 6.97"



**\*63401**

**3 Light Wall**

Amber Bronze Finish with White Alabaster Glass

Height: 9.76" Width: 22.83" Extends: 8.35"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum




\*Fixture can be Pendant or Semi-Flush Mount

\*Fixture can be installed up or down

# Dunmore Collection

Fluid, curled arms add a touch of class.



**63061**  
**1 Light Mini Pendant**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 37.68"  
 Diameter: 6.14"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum  
 Includes (3) 9.5" long rods.  
 Install 1, 2, or 3 rods for customized lengths.



**63065**  
**2 Light Semi-Flush**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 12.32" Diameter: 14.49"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63062**  
**2 Light Flush**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 6.42" Diameter: 12.99"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63066**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 9.49" Width: 6.14" Extends: 9.25"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**\*63069**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 9.57" Width: 23.46" Extends: 7.50"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63068**  
**2 Light Wall**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 9.61" Width: 15.51" Extends: 8.19"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63070**  
**4 Light Wall**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 9.25" Width: 31.5" Extends: 7.50"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum

\*Fixture can be installed up or down

# Dunmore Collection

Fluid, curled arms add a touch of class.



**63057**  
**5 Light Chandelier**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 23.50" Diameter: 23.50" Chain: 36" Cord: 60"  
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



**85046**  
**Frosted Flared Cone Shade**  
 Fitter: 2.25"  
 Height: 5.32"  
 Diameter: 6.14"

**63060**  
**1 Light Pendant**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 13.46" Diameter: 15.20"  
 Chain: 36" Cord: 60"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63059**  
**2 Light Island Pendant**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 18.54" Width: 37"  
 Chain: 36" Cord: 60"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63058**  
**3 Light Pendant**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 23.58" Diameter: 16.57"  
 Chain: 36" Cord: 60"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum





# Harwell Collection


Traditional style in a wide variety of fixtures provides options for a cohesive look.



**63048**  
**2 Light Flush**  
 Amber Bronze Finish  
 with Frosted Glass  
 Height: 6.14" Diameter: 12.99"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**†63044**  
**3 Light Pendant/Semi-Flush**  
 Amber Bronze Finish  
 with Frosted Glass  
 Height: 17.87" Diameter: 16.06"  
 Chain: 36" Cord: 60"  
 Use (3) Medium (E26)  
 Base Lamps, 60 Watt Maximum




**63043**  
**1 Light Pendant**  
 Amber Bronze Finish  
 with Frosted Glass  
 Height: 9.65" Diameter: 15.91"  
 Chain: 36" Cord: 60"  
 Use (1) Medium (E26)  
 Base Lamp,  
 60 Watt Maximum



**\*63049**  
**3 Light Wall**  
 Amber Bronze Finish with White Opal Glass  
 Height: 8.50" Width: 24.35" Extends: 7.76"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\*85043**  
**White Opal  
 Bell Shade**  
 Fitter: 2.25"  
 Height: 4.88"  
 Diameter: 6.61"



**63047**  
**1 Light  
 Mini Pendant**  
 Amber Bronze Finish  
 with White Opal Glass  
 Height: 37.71" Diameter: 6.61"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum  
 Includes (3) 9.5" long rods.  
 Install 1, 2, or 3 rods for  
 customized lengths.



**\*63051**  
**4 Light Wall**  
 Amber Bronze Finish with White Opal Glass  
 Height: 8.50" Width: 32.60" Extends: 7.76"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63052**  
**5 Light Wall**  
 Amber Bronze Finish with White Opal Glass  
 Height: 8.50" Width: 41.42" Extends: 7.76"  
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



**63042**  
**5 Light Chandelier**  
 Amber Bronze Finish  
 with White Opal Glass  
 Height: 16.24"  
 Diameter: 22.64"  
 Chain: 36" Cord: 60"  
 Use (5) Medium (E26)  
 Base Lamps,  
 60 Watt Maximum

- Hand Blown Glass
- †Fixture can be Pendant or Semi-Flush Mount
- Fixture can be installed up or down

# Harwell Collection

Traditional style in a wide variety of fixtures provides options for a cohesive look.



**63056**  
**2 Light Flush**  
 Brushed Nickel Finish  
 with Frosted Glass  
 Height: 6.14" Diameter: 12.99"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**\*63054**  
**3 Light Pendant/Semi-Flush**  
 Brushed Nickel Finish  
 with Frosted Glass  
 Height: 17.87" Diameter: 16.06"  
 Chain: 36" Cord: 60"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum




**63004**  
**1 Light Pendant**  
 Brushed Nickel Finish  
 with Frosted Glass  
 Height: 9.65" Diameter: 15.91"  
 Chain: 36" Cord: 60"  
 Use (1) Medium (E26)  
 Base Lamp,  
 60 Watt Maximum



**\*63015**  
**3 Light Wall**  
 Brushed Nickel Finish with White Opal Glass  
 Height: 8.50" Width: 24.35" Extends: 7.76"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\*85043**  
**White Opal  
 Bell Shade**  
 Fitter: 2.25"  
 Height: 4.88"  
 Diameter: 6.61"



**63007**  
**1 Light  
 Mini Pendant**  
 Brushed Nickel Finish  
 with White Opal Glass  
 Height: 37.71" Diameter: 6.61"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum  
 Includes (3) 9.5" long rods.  
 Install 1, 2, or 3 rods for  
 customized lengths.



**\*63019**  
**4 Light Wall**  
 Brushed Nickel Finish with White Opal Glass  
 Height: 8.50" Width: 32.60" Extends: 7.76"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63020**  
**5 Light Wall**  
 Brushed Nickel Finish with White Opal Glass  
 Height: 8.50" Width: 41.42" Extends: 7.76"  
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



**63001**  
**5 Light Chandelier**  
 Brushed Nickel Finish  
 with White Opal Glass  
 Height: 16.24"  
 Diameter: 22.64"  
 Chain: 36" Cord: 60"  
 Use (5) Medium (E26)  
 Base Lamps,  
 60 Watt Maximum

•Hand Blown Glass  
 \*Fixture can be Pendant or Semi-Flush Mount  
 •Fixture can be installed up or down

# Parker Mews Collection

Brighten your space with this elegant collection featuring clean lines and rich fabric shades.



**62260**  
**1 Light Wall**  
 Brushed Nickel Finish  
 with White Linen Fabric Shade  
 Height: 9.75" Width: 5.50" Extends: 7"  
 Use (1) Candelabra (E12) Base Lamp,  
 60 Watt Maximum



**62259**  
**2 Light Flush**  
 Brushed Nickel Finish  
 with White Linen Fabric Shade  
 Height: 6" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**62257**  
**2 Light Semi-Flush**  
 Brushed Nickel Finish  
 with White Linen Fabric Shade  
 Height: 10.75" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum

# Sylvestre Collection

Sleek design adds modern flair to any space.



\* **62278**  
**1 Light Wall**  
 Brushed Nickel Finish  
 with Frosted Seeded Glass  
 Height: 8.25" Width: 4.75" Extends: 6.25"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



\* **62279**  
**3 Light Wall**  
 Brushed Nickel Finish  
 with Frosted Seeded Glass  
 Height: 8.25" Width: 15.75" Extends: 6.25"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**62275**  
**3 Light Chandelier**  
 Brushed Nickel Finish with Frosted Seeded Glass  
 Height: 17.63" Diameter: 18.25" Chain: 36" Cord: 120"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**62274**  
**5 Light Chandelier**  
 Brushed Nickel Finish with Frosted Seeded Glass  
 Height: 18.50" Diameter: 20.63" Chain: 36" Cord: 120"  
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum

\*Fixture can be installed up or down

# Packard Collection

Statement-making fabric drum shade adds sophistication to any setting.



**63416**

**2 Light Flush**

Amber Bronze Finish with Beige Fabric Shade and Frosted Glass Panel

Height: 8.25" Diameter: 13"

Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**†63417**

**2 Light Pendant/Semi-Flush**

Amber Bronze Finish with Beige Fabric Shade and Frosted Glass Panel

Height: 17.60" Diameter: 14" Chain: 36" Cord: 60"

Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



# Trinity I & II Collections

Dramatically curved arms and bold oil rubbed bronze finish bring a touch of elegance to your home.

**\*62238**

**1 Light Wall**

Oil Rubbed Bronze Finish with Aged Alabaster Glass

Height: 9" Width: 5.13" Extends: 8"

Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**\*62239**

**3 Light Wall**

Oil Rubbed Bronze Finish with Aged Alabaster Glass

Height: 8.50" Width: 17.25" Extends: 8.38"

Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**62235**

**5 Light Chandelier**

Oil Rubbed Bronze Finish with Aged Alabaster Glass

Height: 11" Width: 23" Chain: 36" Cord: 60"

Use (5) Medium (E26) Base Lamps, 60 Watt Maximum



**\*66496**

**1 Light Wall**

Brushed Nickel Finish with White Opal Glass

Height: 9" Width: 5.13" Extends: 8"

Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**\*64617**

**2 Light Wall**

Brushed Nickel Finish with White Opal Glass

Height: 8.5" Width: 13.50" Extends: 8.50"

Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**\*66497**

**3 Light Wall**

Brushed Nickel Finish with White Opal Glass

Height: 8.50" Width: 17.25" Extends: 8.37"

Use (3) Medium (E26) Base Lamps, 60 Watt Maximum

†Fixture can be Pendant or Semi-Flush Mount

\*Fixture can be installed up or down





# Westinghouse

INNOVATION YOU CAN BE SURE OF



## INDOOR CEILING LIGHT FIXTURES

Inspiration guides our ceiling fixture designs. Westinghouse's wide range of styles and finishes will complement any décor.



# LED SURFACE MOUNT FIXTURES



**Small LED Surface Mount**  
 Chrome Finish with Frosted Lens  
 Height: 1" Diameter: 6"  
 Includes 12 Watt Integrated LED  
**63218** - 3000K  
**63222** - 4000K



**Large LED Surface Mount**  
 Chrome Finish with Frosted Lens  
 Height: 1.37" Diameter: 7.38"  
 Includes 15 Watt Integrated LED  
**63226** - 3000K  
**63230** - 4000K



**Small LED Surface Mount**  
 Brushed Nickel Finish with Frosted Lens  
 Height: 1" Diameter: 6"  
 Includes 12 Watt Integrated LED  
**63219** - 3000K  
**63223** - 4000K



**Large LED Surface Mount**  
 Brushed Nickel Finish with Frosted Lens  
 Height: 1.37" Diameter: 7.38"  
 Includes 15 Watt Integrated LED  
**63227** - 3000K  
**63231** - 4000K



**Small LED Surface Mount**  
 Oil Rubbed Bronze Finish with Frosted Lens  
 Height: 1" Diameter: 6"  
 Includes 12 Watt Integrated LED  
**63220** - 3000K  
**63224** - 4000K



**Large LED Surface Mount**  
 Oil Rubbed Bronze Finish with Frosted Lens  
 Height: 1.37" Diameter: 7.38"  
 Includes 15 Watt Integrated LED  
**63228** - 3000K  
**63232** - 4000K



**Small LED Surface Mount**  
 White Finish with Frosted Lens  
 Height: 1" Diameter: 6"  
 Includes 12 Watt Integrated LED  
**63221** - 3000K  
**63225** - 4000K



**Large LED Surface Mount**  
 White Finish with Frosted Lens  
 Height: 1.37" Diameter: 7.38"  
 Includes 15 Watt Integrated LED  
**63229** - 3000K  
**63233** - 4000K

## DIMMABLE LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Avg. Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
63218	*	12	60	3000 (Warm White)	840	80	50000	45.6	\$1.45
63222	*	12	60	4000 (Warm White)	840	80	50000	45.6	\$1.45
63219	*	12	60	3000 (Warm White)	840	80	50000	45.6	\$1.45
63223	*	12	60	4000 (Warm White)	840	80	50000	45.6	\$1.45
63220	*	12	60	3000 (Warm White)	840	80	50000	45.6	\$1.45
63224	*	12	60	4000 (Warm White)	840	80	50000	45.6	\$1.45
63221	*	12	60	3000 (Warm White)	840	80	50000	45.6	\$1.45
63225	*	12	60	4000 (Warm White)	840	80	50000	45.6	\$1.45
63226	*	15	75	3000 (Warm White)	1050	80	50000	45.6	\$1.81
63230	*	15	75	4000 (Warm White)	1050	80	50000	45.6	\$1.81
63227	*	15	75	3000 (Warm White)	1050	80	50000	45.6	\$1.81
63231	*	15	75	4000 (Warm White)	1050	80	50000	45.6	\$1.81
63228	*	15	75	3000 (Warm White)	1050	80	50000	45.6	\$1.81
63232	*	15	75	4000 (Warm White)	1050	80	50000	45.6	\$1.81
63229	*	15	75	3000 (Warm White)	1050	80	50000	45.6	\$1.81
63233	*	15	75	4000 (Warm White)	1050	80	50000	45.6	\$1.81

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

\* Integrated LED Light Source

# CEILING LIGHT FIXTURE ASSORTMENT

**63088**

**11" LED Flush**

Brushed Nickel Finish  
with White Alabaster Glass  
Height: 3.46" Diameter: 11"

Includes 16 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**63089**

**11" LED Flush**

Oil Rubbed Bronze Finish  
with White Alabaster Glass  
Height: 3.46" Diameter: 11"

Includes 16 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED



INTEGRATED  
DIMMABLE  
LED

**64005**

**11" LED Flush**

Brushed Nickel Finish  
with White Alabaster Glass  
Height: 4.75" Diameter: 11"

Includes 15 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64012**

**15 3/4" LED Flush**

Brushed Nickel Finish  
with White Acrylic Shade  
Height: 3.50" Diameter: 15.75"

Includes 23 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64009**

**11 7/8" LED Semi-Flush**

Brushed Nickel Finish  
with White Acrylic Shade  
Height: 9.50" Diameter: 11.88"

Includes 15 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64006**

**11" LED Flush**

Oil Rubbed Bronze Finish  
with White Alabaster Glass  
Height: 4.75" Diameter: 11"

Includes 15 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64007**

**11" LED Flush**

Oil Rubbed Bronze Finish  
with White Alabaster Glass  
Height: 4.63" Diameter: 11"

Includes 14.5 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**64008**

**11" LED Flush**

Oil Rubbed Bronze Finish  
with White Alabaster Glass  
Height: 4.63" Diameter: 11"

Includes 12 Watt Integrated LED

## DIMMABLE LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
64088	*	16	75	3000 (Warm White)	1000	80	30000	27.3	\$1.93
64089	*	16	75	3000 (Warm White)	1000	80	30000	27.3	\$1.93
64005	*	15	60	3000 (Warm White)	930	80	30000	27.3	\$1.75
64012	*	23	100	3000 (Warm White)	1600	80	30000	27.3	\$2.77
64009	*	15	75	3000 (Warm White)	1000	80	30000	27.3	\$1.81
64006	*	15	60	3000 (Warm White)	930	80	30000	27.3	\$1.81
64007	*	14.5	60	3000 (Warm White)	930	80	30000	27.3	\$1.75
64008	*	12	40	3000 (Warm White)	730	80	30000	27.3	\$1.45

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

\* Integrated LED Light Source



**†63417**  
**Packard**  
**2 Light Pendant/Semi-Flush**  
 Amber Bronze Finish with Beige Fabric Shade and Frosted Glass Panel  
 Height: 17.60" Diameter: 14"  
 Chain: 36" Cord: 60"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63416**  
**Packard**  
**2 Light Flush**  
 Amber Bronze Finish with Beige Fabric Shade and Frosted Glass Panel  
 Height: 8.25" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63048**  
**Harwell**  
**2 Light Flush**  
 Amber Bronze Finish with Frosted Glass  
 Height: 6.14" Diameter: 12.99"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**62259**  
**Parker Mews**  
**2 Light Flush**  
 Brushed Nickel Finish with White Linen Fabric Shade  
 Height: 6" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**62257**  
**Parker Mews**  
**2 Light Semi-Flush**  
 Brushed Nickel Finish with White Linen Fabric Shade  
 Height: 10.75" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63056**  
**Harwell**  
**2 Light Flush**  
 Brushed Nickel Finish with Frosted Glass  
 Height: 6.14" Diameter: 12.99"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**66223**  
**Wensley**  
**2 Light Semi-Flush**  
 Oil Rubbed Bronze Finish with White Alabaster Glass  
 Height: 6.50" Diameter: 10.13"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**†63403**  
**Pacific Falls**  
**2 Light Pendant/Semi-Flush**  
 Amber Bronze Finish with White Alabaster Glass  
 Height: 13.86" Diameter: 13.98"  
 Chain: 36" Cord: 60"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63065**  
**Dunmore**  
**2 Light Semi-Flush**  
 Oil Rubbed Bronze Finish with Frosted Glass  
 Height: 12.32" Diameter: 14.49"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum

†Fixture can be Pendant or Semi-Flush Mount

## CEILING LIGHT FIXTURE ASSORTMENT

**63023****Malvern****2 Light Flush***Oil Rubbed Bronze Finish  
with Smoldering Scavo Glass**Height: 6.85" Diameter: 12.99"**Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***63030****Midori****2 Light Flush***Oil Rubbed Bronze Finish  
with Amber Linen Glass**Height: 6.57" Diameter: 12.99"**Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***63405****Callan****2 Light Flush***Oil Rubbed Bronze Finish  
with Caramel Scavo Glass**Height: 6.65" Diameter: 13"**Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***63414****Karah****3 Light Flush***Oil Rubbed Bronze Finish  
with Aged Amber Scavo Glass**Height: 6.53" Diameter: 15"**Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum***63413****Karah****2 Light Flush***Oil Rubbed Bronze Finish  
with Aged Amber Scavo Glass**Height: 5.63" Diameter: 12"**Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***63426****Tolbut****3 Light Flush***Oil Rubbed Bronze Finish  
with Amber Alabaster Glass**Height: 6.18" Diameter: 15"**Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum***63424****Tolbut****2 Light Flush***Oil Rubbed Bronze Finish  
with Amber Alabaster Glass**Height: 5.51" Diameter: 12.99"**Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***63400****Pacific Falls****2 Light Flush***Amber Bronze Finish  
with White Alabaster Glass**Height: 6.89" Diameter: 13"**Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***63432****Montrose****2 Light Flush***Oil Rubbed Bronze Finish  
with Highlights and Mocha Scavo Glass**Height: 6.81" Diameter: 13"**Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***63062****Dunmore****2 Light Flush***Oil Rubbed Bronze Finish  
with Frosted Glass**Height: 6.42" Diameter: 12.99"**Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum*





**63422**  
**Scholar**  
**1 Light Semi-Flush**  
*Oil Rubbed Bronze Finish with White Opal Glass*  
 Height: 9.06" Diameter: 7.36"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63427**  
**Wilkes**  
**2 Light Flush**  
*Gun Metal Finish with Lunar Weave Glass*  
 Height: 4.25" Square: 11"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63408**  
**Ewing**  
**2 Light Flush**  
*Oil Rubbed Bronze Finish with Amber Linen Glass*  
 Height: 4.25" Square: 11"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63410**  
**Karah**  
**3 Light Flush**  
*Brushed Nickel Finish with White Linen Glass*  
 Height: 6.53" Diameter: 15"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**63409**  
**Karah**  
**2 Light Flush**  
*Brushed Nickel Finish with White Linen Glass*  
 Height: 5.63" Diameter: 12"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63425**  
**Tolbut**  
**3 Light Flush**  
*Antique Silver Finish with White Alabaster Glass*  
 Height: 6.18" Diameter: 15"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**63423**  
**Tolbut**  
**2 Light Flush**  
*Antique Silver Finish with White Alabaster Glass*  
 Height: 5.51" Diameter: 12.99"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**63444**  
**2 Light Flush, 2-Pack**  
*Brushed Nickel Finish with Frosted Swirl Glass*  
 Height: 6.65" Diameter: 13"  
 Use (2) Medium Base (E26) Base Lamps, 60 Watt Maximum



**63445**  
**2 Light Flush, 2-Pack**  
*Oil Rubbed Bronze Finish with Frosted Swirl Glass*  
 Height: 6.65" Diameter: 13"  
 Use (2) Medium Base (E26) Base Lamps, 60 Watt Maximum



**63446**  
**2 Light Flush, 2-Pack**  
*White Finish with Frosted Swirl Glass*  
 Height: 6.65" Diameter: 13"  
 Use (2) Medium Base (E26) Base Lamps, 60 Watt Maximum

## CEILING LIGHT FIXTURE ASSORTMENT

**64300****2 Light Flush***White Finish  
with Frosted Swirl Glass**Height: 6.13" Diameter: 13"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***64301****3 Light Flush***White Finish  
with Frosted Swirl Glass**Height: 6.50" Diameter: 15"  
Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum***66162****2 Light Flush***Textured White Finish  
with Embossed Floral and  
Leaf Design Glass**Height: 7" Diameter: 13.25"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***64316****2 Light Flush***Sienna Finish  
with Embossed Floral and  
Leaf Design Glass**Height: 7" Diameter: 13"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***66327****1 Light Flush***Polished Brass Finish  
with Frosted Swirl Glass**Height: 5.88" Diameter: 11"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum***64302****2 Light Flush***Polished Brass Finish  
with Frosted Swirl Glass**Height: 6.13" Diameter: 13"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***64303****3 Light Flush***Polished Brass Finish  
with Frosted Swirl Glass**Height: 6.50" Diameter: 15"  
Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum***64304****1 Light Flush***Brushed Nickel Finish  
with Frosted Swirl Glass**Height: 5.88" Diameter: 11"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum***64305****2 Light Flush***Brushed Nickel Finish  
with Frosted Swirl Glass**Height: 6.13" Diameter: 13"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum***64306****3 Light Flush***Brushed Nickel Finish  
with Frosted Swirl Glass**Height: 6.50" Diameter: 15"  
Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum*



**67572**  
**Eastgate**  
**1 Light Flush**  
 Brushed Nickel Finish  
 with Frosted White Alabaster Glass  
 Height: 5.25" Diameter: 10.25"  
 Use (1) Medium (E26) Base Lamp,  
 75 Watt Maximum



**67573**  
**Eastgate**  
**2 Light Flush**  
 Brushed Nickel Finish  
 with Frosted White Alabaster Glass  
 Height: 5.50" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**64360**  
**3 Light Flush**  
 Brushed Nickel Finish  
 with Frosted White Alabaster Glass  
 Height: 6.75" Diameter: 15"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**64290**  
**1 Light Flush**  
 Oil Rubbed Bronze Finish  
 with Frosted White Alabaster Glass  
 Height: 5.50" Diameter: 11"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**64291**  
**2 Light Flush**  
 Oil Rubbed Bronze Finish  
 with Frosted White Alabaster Glass  
 Height: 5.88" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**64292**  
**3 Light Flush**  
 Oil Rubbed Bronze Finish  
 with Frosted White Alabaster Glass  
 Height: 6.63" Diameter: 15"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**64340**  
**2 Light Semi-Flush**  
 Brushed Nickel Finish  
 with Frosted Glass  
 Height: 8" Diameter: 15.25"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**66282**  
**2 Light Flush**  
 Polished Brass Finish  
 with Crystal Ribbed Glass  
 Height: 7.25" Diameter: 13.50"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum

## CEILING LIGHT FIXTURE ASSORTMENT

**67209****1 Light Flush**

Brushed Nickel Finish  
with Frosted Fluted Glass

Height: 4" Diameter: 6.88"

Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum

**67210****2 Light Flush with Pull Chain**

Brushed Nickel Finish  
with Frosted Fluted Glass

Height: 4.25" Diameter: 8.75"

Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum

**67215****2 Light Flush with Pull Chain**

Polished Brass Finish  
with Frosted Fluted Glass

Height: 4.25" Diameter: 8.75"

Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum

**66699****1 Light Flush**

White Finish  
with White Glass

Height: 4.38" Diameter: 7.25"

Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum

**66611****2 Light Flush**

White Finish  
with White Glass

Height: 5" Diameter: 8.75"

Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum

**67202****2 Light Flush with Pull Chain**

Sienna Finish  
with Frosted Fluted Glass

Height: 4.25" Diameter: 8.75"

Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum

**66689****1 Light Flush**

Polished Brass Finish  
with Clear Faceted Glass

Height: 4.75" Diameter: 7.50"

Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum

**66610****2 Light Flush**

Antique Brass Finish  
with Clear Faceted Glass

Height: 5.50" Diameter: 9.50"

Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum

**66609****2 Light Flush**

Polished Brass Finish  
with White Glass

Height: 4.75" Diameter: 8.88"

Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum





**66658**

**1 Light Flush**

Polished Brass Finish  
with Clear Acorn Design Glass  
Height: 7.25" Diameter: 5.25"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum



**66692**

**1 Light Flush**

Polished Brass Finish  
with Crystal Ribbed Glass Globe  
Height: 7.25" Diameter: 6"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum



**67208**

**1 Light Flush  
with Pull Chain**

Brushed Nickel Finish  
with White Glass Globe  
Height: 7.25" Diameter: 6"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum



**66214**

**3 Light Flush**

White Finish  
with White Glass Globes  
Height: 7.25" Diameter: 16"  
Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum



**66680**

**1 Light Flush  
with Pull Chain**

White Finish  
with White Glass Globe  
Height: 7.25" Diameter: 6"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum



**66607**

**1 Light Flush**

White Finish  
with White Glass Globe  
Height: 7.25" Diameter: 6"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum



**66686**

**3 Light Flush**

Antique Brass Finish  
with Frosted Ruffled Edge Glass  
Height: 5.63" Width: 11"  
Use (3) Medium (E26) Base Lamps,  
60 Watt Maximum



**66326**

**3 Light Multi-Directional Flush**

White Finish  
Height: 8.25" Width: 10.13" Extends: 18.25"  
Use (3) Medium (E26) Base Lamps,  
R30/BR30, 65 Watt Maximum



**66624**

**1 Light Multi-Directional Flush**

White Finish  
Height: 8.25" Width: 5.50" Extends: 9"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum

## CEILING LIGHT FIXTURE ASSORTMENT

**66204****1 Light Flush**

White Finish  
with White and Clear Glass  
Height: 4.50" Diameter: 6.75"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum

**66203****2 Light Flush**

White Finish  
with White and Clear Glass  
Height: 5.25" Diameter: 8.75"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum

**66238****2 Light Flush**

White Finish  
with White and Clear Glass  
Height: 5.25" Diameter: 10.75"  
Use (2) Medium (E26) Base Lamps,  
75 Watt Maximum

**66239****1 Light Flush**

Chrome Finish  
with White and Clear Glass  
Height: 4.50" Diameter: 6.75"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum

**66240****2 Light Flush**

Chrome Finish  
with White and Clear Glass  
Height: 5.25" Diameter: 8.75"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum

**66241****2 Light Flush**

Chrome Finish  
with White and Clear Glass  
Height: 5.25" Diameter: 10.75"  
Use (2) Medium (E26) Base Lamps,  
75 Watt Maximum

**67345****2 Light Flush  
with Pull Chain**

White Finish  
with White and Clear Glass  
Height: 5.25" Diameter: 8.75"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum



INTEGRATED  
DIMMABLE  
LED



**62049**  
**8 7/8" LED Round Flush**  
 White Finish with  
 Frosted Polycarbonate Panel  
 Height: 1.50" Diameter: 8.86"  
 Includes 14 Watt Integrated LED

INTEGRATED  
DIMMABLE  
LED



**62050**  
**8 7/8" LED Square Flush**  
 White Finish with  
 Frosted Polycarbonate Panel  
 Height: 1.50" Square: 8.86"  
 Includes 14 Watt Integrated LED

INTEGRATED  
LED



**64011**  
**11" LED Flush**  
 White Finish with  
 White Acrylic Shade  
 Height: 3.50" Diameter: 11"  
 Includes 15 Watt Integrated LED

**LED LIGHT SOURCE SPECIFICATIONS**

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
62049	*	14	60	3000 (Warm White)	800	80	30000	27.3	\$1.69
62050	*	14	60	3000 (Warm White)	800	80	30000	27.3	\$1.69
64011	*	15	75	3000 (Warm White)	1000	80	30000	27.3	\$1.81

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).  
 \* Integrated LED Light Source

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh



**66297**  
**1 Light Flush**  
 White and Brushed Nickel Finish  
 with White Alabaster Glass  
 Height: 4.25" Diameter: 12"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**66206**  
**2 Light Semi-Flush**  
 White Finish  
 with White Scroll Design Glass  
 Height: 6.25" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**66242**  
**2 Light Semi-Flush**  
 White Finish  
 with White Glass  
 Height: 6.50" Diameter: 13"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**66201**  
**2 Light Semi-Flush**  
 White Finish  
 with White Glass  
 Height: 6" Square: 12"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**66263**  
**2 Light Semi-Flush**  
 White Finish  
 with White and Clear Glass  
 Height: 6.25" Square: 11.5"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**66200**  
**2 Light Semi-Flush with Pull Chain**  
 White Finish  
 with White Glass  
 Height: 6.63" Square: 12"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



# Westinghouse

INNOVATION YOU CAN BE SURE OF



## INDOOR WALL LIGHT FIXTURES

Utilize the versatility of wall fixtures to enhance the beauty of a fireplace, accentuate nooks and quiet spaces, or add a decorative touch around a bathroom mirror. The possibilities are endless.



# WALL LIGHT FIXTURE ASSORTMENT



INTEGRATED  
DIMMABLE  
LED

**\*63076**  
**1 Light LED Wall**  
Chrome Finish with Bubble Glass  
Height: 7.76" Width: 4.96"  
Extends: 5.69"  
Includes 8 Watt Integrated LED



INTEGRATED  
DIMMABLE  
LED

**\*63077**  
**2 Light LED Wall**  
Chrome Finish with Bubble Glass  
Height: 7.76" Width: 9.46" Extends: 5.69"  
Includes 2 x 7.5 Watt Integrated LEDs



INTEGRATED  
DIMMABLE  
LED

**\*63119**  
**3 Light LED Wall**  
Chrome Finish with Bubble Glass  
Height: 7.76" Width: 15.16" Extends: 5.69"  
Includes 3 x 7.33 Watt Integrated LEDs

## DIMMABLE LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
63076	*	8	40	3000 (Warm White)	360	80	25000	22.8	\$0.96
63077	*	15	80 (2 x 40)	3000 (Warm White)	730	80	25000	22.8	\$1.81
63119	*	22	120 (3 x 40)	3000 (Warm White)	1300	80	25000	22.8	\$2.65

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).  
\* Integrated LED Light Source

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh



**\*63025**  
**Ramsgate**  
**1 Light Wall**  
Brushed Nickel Finish with Ice Glass  
Height: 9" Width: 5.12" Extends: 7.50"  
Use (1) Medium (E26) Base Lamp, 60 Watt Maximum  
•Replacement Glass #85006



**\*63026**  
**Ramsgate**  
**2 Light Wall**  
Brushed Nickel Finish with Ice Glass  
Height: 9" Width: 12" Extends: 6.50"  
Use (2) Medium (E26) Base Lamps, 60 Watt Maximum  
•Replacement Glass #85006



**\*63081**  
**Ramsgate**  
**3 Light Wall**  
Brushed Nickel Finish with Ice Glass  
Height: 9" Width: 20" Extends: 7.50"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
•Replacement Glass #85006

•Hand Blown Glass  
\*Fixture can be installed up or down

## WALL LIGHT FIXTURE ASSORTMENT

Height shown for Iron Hill fixtures is without lamps.



**63449**  
**Iron Hill**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Highlights and Metallic Bronze Interior  
 Height: 7.38" Width: 29.09" Extends: 9.65"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**63448**  
**Iron Hill**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Highlights and Metallic Bronze Interior  
 Height: 7.90" Width: 8.67" Extends: 9.65"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63434**  
**Iron Hill**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish with Highlights  
 Height: 7.38" Width: 29.09" Extends: 9.65"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**63435**  
**Iron Hill**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish with Highlights  
 Height: 7.90" Width: 8.67" Extends: 9.65"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63421**  
**Scholar**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish with White Opal Glass  
 Height: 9.96" Width: 24.02" Extends: 7.99"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



 **Westinghouse**  
**VINTAGE LAMPS**

Add Westinghouse Filament  
 LED or Timeless lamps for  
 the vintage look you want.



**\*63021**  
**Malvern**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Smoldering Scavo Glass  
 Height: 12.36" Width: 5.12"  
 Extends: 7.17"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum  
**Replacement Glass #81017**



**\*63022**  
**Malvern**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Smoldering Scavo Glass  
 Height: 11.85" Width: 19.69"  
 Extends: 8.74"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum  
**Replacement Glass #81017**

\*Fixture can be installed up or down



**\*63073**  
Midori  
**1 Light Wall**  
*Oil Rubbed Bronze Finish with Amber Linen Glass*  
Height: 8.54" Width: 5.12" Extends: 7.09"  
Use (1) Medium (E26) Base Lamp, 60 Watt Maximum  
• **Replacement Glass #81009**



**\*63074**  
Midori  
**2 Light Wall**  
*Oil Rubbed Bronze Finish with Amber Linen Glass*  
Height: 10.71" Width: 14.96" Extends: 7.09"  
Use (2) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #81009**



**\*63075**  
Midori  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Amber Linen Glass*  
Height: 10.12" Width: 20.87" Extends: 7.09"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #81009**



**▲\*63442C**  
Ewing  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Smoldering Scavo Glass*  
Height: 8.31" Width: 20.47" Extends: 6.89"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
**Replacement Glass #81017**



**▲\*63442A**  
Ewing  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Amber Linen Glass*  
Height: 7.80" Width: 20.87" Extends: 7.09"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #81009**



**▲\*63442B**  
Ewing  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Amber Harvest Glass*  
Height: 7.80" Width: 19.69" Extends: 6.5"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #81015**



**\*63415**  
Karah  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Aged Amber Scavo Glass*  
Height: 7.72" Width: 22" Extends: 7.09"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #81004**

• Hand Blown Glass

▲ Design Collection

\* Fixture can be installed up or down

## WALL LIGHT FIXTURE ASSORTMENT



**\*63039**  
 Alexander  
**2 Light Wall**  
 Brushed Nickel Finish with Rippled White Glazed Glass  
 Height: 11.14" Width: 15.24" Extends: 5.90"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum  
 • **Replacement Glass #85045**



**\*63040**  
 Alexander  
**3 Light Wall**  
 Brushed Nickel Finish with Rippled White Glazed Glass  
 Height: 11.14" Width: 22.50" Extends: 5.90"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
 • **Replacement Glass #85045**



**\*63041**  
 Alexander  
**4 Light Wall**  
 Brushed Nickel Finish with Rippled White Glazed Glass  
 Height: 11.14" Width: 30.24" Extends: 5.90"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum  
 • **Replacement Glass #85045**



**▲\* 63438C**  
 Hansen  
**3 Light Wall**  
 Chrome Finish with Glazed Ice Glass  
 Height: 8.66" Width: 20.75" Extends: 7.05"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
 • **Replacement Glass #81018**



**▲\* 63438A**  
 Hansen  
**3 Light Wall**  
 Chrome Finish  
 with White Linen Glass and Translucent Band  
 Height: 7.80" Width: 19.69" Extends: 6.50"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
 • **Replacement Glass #81014**



**▲\* 63438B**  
 Hansen  
**3 Light Wall**  
 Chrome Finish with White Linen Glass  
 Height: 7.80" Width: 19.69" Extends: 6.50"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
 • **Replacement Glass #81016**

• Hand Blown Glass

▲ Design Collection

\* Fixture can be installed up or down





**\*63428**  
**Montrose**  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Highlights and Mocha Scavo Glass*  
*Height: 10.67" Width: 19" Extends: 8.50"*  
*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*  
**•Replacement Glass #81005**



**63027**  
**Lenola**  
**2 Light Wall**  
*Amber Bronze Finish with Beige Fabric Shades*  
*Height: 13.58" Width: 16.57" Extends: 7.87"*  
*Use (2) Candelabra (E12) Base Lamps, 40 Watt Maximum*



**63028**  
**Lenola**  
**3 Light Wall**  
*Amber Bronze Finish with Beige Fabric Shades*  
*Height: 12.76" Width: 23.9" Extends: 7.87"*  
*Use (3) Candelabra (E12) Base Lamps, 40 Watt Maximum*



**\*63066**  
**Dunmore**  
**1 Light Wall**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
*Height: 9.49" Width: 6.14" Extends: 9.25"*  
*Use (1) Medium (E26) Base Lamp, 60 Watt Maximum*  
**Replacement Glass #85046**



**\*63069**  
**Dunmore**  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
*Height: 9.57" Width: 23.46" Extends: 7.50"*  
*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*  
**Replacement Glass #85046**



**\*63068**  
**Dunmore**  
**2 Light Wall**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
*Height: 9.61" Width: 15.51" Extends: 8.19"*  
*Use (2) Medium (E26) Base Lamps, 60 Watt Maximum*  
**Replacement Glass #85046**



**\*63070**  
**Dunmore**  
**4 Light Wall**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
*Height: 9.25" Width: 31.5" Extends: 7.50"*  
*Use (4) Medium (E26) Base Lamps, 60 Watt Maximum*  
**Replacement Glass #85046**

•Hand Blown Glass

\*Fixture can be installed up or down

## WALL LIGHT FIXTURE ASSORTMENT




**\*63406**  
**Callan**  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Caramel Scavo Glass*  
 Height: 7.75" Width: 24" Extends: 8.86"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
**Replacement Glass #81002**



**\*63401**  
**Pacific Falls**  
**3 Light Wall**  
*Amber Bronze Finish with White Alabaster Glass*  
 Height: 9.76" Width: 22.83" Extends: 8.35"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
**Replacement Glass #81000**



**▲\*63437A**  
**Wilkes**  
**3 Light Wall**  
*Gun Metal Finish with Lunar Weave Glass*  
 Height: 10.35" Width: 21.85" Extends: 6.46"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
**• Replacement Glass #81006**



**▲\*63437B**  
**Wilkes**  
**3 Light Wall**  
*Gun Metal Finish with White Linen Glass*  
 Height: 10.35" Width: 21.85" Extends: 6.46"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
**• Replacement Glass #81013**



**\*63034**  
**Elvaston**  
**3 Light Wall**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
 Height: 8.86" Width: 23.07" Extends: 7.48"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
**Replacement Glass #85047**



**\*63035**  
**Elvaston**  
**4 Light Wall**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
 Height: 8.50" Width: 31" Extends: 7.48"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum  
**Replacement Glass #85047**



**\*63036**  
**Elvaston**  
**5 Light Wall**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
 Height: 9.25" Width: 39" Extends: 7.48"  
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum  
**Replacement Glass #85047**

- Hand Blown Glass
- ▲ Design Collection
- \* Fixture can be installed up or down



**\*63015**  
Harwell  
**3 Light Wall**  
Brushed Nickel Finish with White Opal Glass  
Height: 8.50" Width: 24.35" Extends: 7.76"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #85043**



**\*63019**  
Harwell  
**4 Light Wall**  
Brushed Nickel Finish with White Opal Glass  
Height: 8.50" Width: 32.6" Extends: 7.76"  
Use (4) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #85043**



**\*63020**  
Harwell  
**5 Light Wall**  
Brushed Nickel Finish with White Opal Glass  
Height: 8.50" Width: 41.42" Extends: 7.76"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #85043**



**\*63049**  
Harwell  
**3 Light Wall**  
Amber Bronze Finish with White Opal Glass  
Height: 8.50" Width: 24.35" Extends: 7.76"  
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #85043**



**\*63051**  
Harwell  
**4 Light Wall**  
Amber Bronze Finish with White Opal Glass  
Height: 8.50" Width: 32.6" Extends: 7.76"  
Use (4) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #85043**



**\*63052**  
Harwell  
**5 Light Wall**  
Amber Bronze Finish with White Opal Glass  
Height: 8.50" Width: 41.42" Extends: 7.76"  
Use (5) Medium (E26) Base Lamps, 60 Watt Maximum  
• **Replacement Glass #85043**



**\*66522**  
**3 Light Wall**  
Chrome Finish with Frosted Pleated Glass  
Height: 8.50" Width: 24" Extends: 7.25"  
Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



**\*66523**  
**4 Light Wall**  
Chrome Finish with Frosted Pleated Glass  
Height: 8.50" Width: 30" Extends: 7.25"  
Use (4) Medium (E26) Base Lamps, 100 Watt Maximum

• **Hand Blown Glass**  
\*Fixture can be installed up or down

## WALL LIGHT FIXTURE ASSORTMENT



**62260**  
**Parker Mews**  
**1 Light Wall**  
 Brushed Nickel Finish  
 with White Linen Fabric Shade  
 Height: 9.75" Width: 5.50" Extends: 7"  
 Use (1) Candelabra (E12)  
 Base Lamp, 60 Watt Maximum



**\*62278**  
**Sylvestre**  
**1 Light Wall**  
 Brushed Nickel Finish  
 with Frosted Seeded Glass  
 Height: 8.25" Width: 4.75" Extends: 6.25"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum



**\*62279**  
**Sylvestre**  
**3 Light Wall**  
 Brushed Nickel Finish  
 with Frosted Seeded Glass  
 Height: 8.25" Width: 15.75" Extends: 6.25"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**\*66496**  
**Trinity**  
**1 Light Wall**  
 Brushed Nickel Finish  
 with White Opal Glass  
 Height: 9" Width: 5.13" Extends: 8"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**\*64617**  
**Trinity**  
**2 Light Wall**  
 Brushed Nickel Finish  
 with White Opal Glass  
 Height: 8.50" Width: 13.50" Extends: 8.50"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**\*66497**  
**Trinity**  
**3 Light Wall**  
 Brushed Nickel Finish  
 with White Opal Glass  
 Height: 8.50" Width: 17.25" Extends: 8.37"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**\*67514**  
**1 Light Wall with On/Off Switch**  
 Oyster Bronze Finish  
 with Frosted Ribbed Design Glass  
 Height: 8" Width: 4.75" Extends: 9.50"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**\*62238**  
**Trinity II**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Aged Alabaster Glass  
 Height: 9" Width: 5.13" Extends: 8"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**\*62239**  
**Trinity II**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish  
 with Aged Alabaster Glass  
 Height: 8.50" Width: 17.25" Extends: 8.38"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**66402**  
**1 Light Wall with Ground Convenience  
 Outlet and Pull Chain**  
 Chrome Finish Base  
 with White and Crystal Glass  
 Height: 4.75" Width: 5.25" Extends: 7.25"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**66601**  
**1 Light Wall with On/Off Switch**  
 Polished Brass Finish  
 with Frosted Etched Grape Design Glass  
 Height: 7.75" Width: 4.50" Extends: 4.87"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**66654**  
**1 Light Wall with On/Off Switch**  
 Brushed Nickel Finish  
 with White Opal Glass  
 Height: 8" Width: 4.50" Extends: 5"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum

\*Fixture can be installed up or down





**\*66401**  
**1 Light Wall**  
 White Finish Base  
 with White Ceramic Glass  
 Height: 7.50" Width: 4.50" Extends: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 75 Watt Maximum



**66403**  
**2 Light Wall with Ground Convenience Outlet**  
 White Finish Base with White Ceramic Glass  
 Height: 4.50" Width: 14" Extends: 5"  
 Use (2) Medium (E26) Base Lamps, 75 Watt Maximum



**66424**  
**4 Light Wall with Ground Convenience Outlet**  
 White Finish Base with White Ceramic Glass  
 Height: 4.25" Width: 24" Extends: 5"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**66594**  
**3 Light Bath Bar**  
 White Finish  
 Height: 4.50" Width: 18" Extends without Lamps: 2.12"  
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



**66595**  
**4 Light Bath Bar**  
 White Finish  
 Height: 4.50" Width: 24" Extends without Lamps: 2.12"  
 Use (4) Medium (E26) Base Lamps, 100 Watt Maximum



**66406**  
**3 Light Bath Bar**  
 Chrome Finish  
 Height: 4.50" Width: 18" Extends without Lamps: 2.12"  
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



**66411**  
**4 Light Bath Bar**  
 Chrome Finish  
 Height: 4.50" Width: 24" Extends without Lamps: 2.12"  
 Use (4) Medium (E26) Base Lamps, 100 Watt Maximum



**66414**  
**6 Light Bath Bar**  
 Chrome Mirror  
 Height: 4.50" Width: 36"  
 Extends without Lamps: 2.12"  
 Use (6) Medium (E26) Base Lamps, 100 Watt Maximum



**66448**  
**3 Light Bath Bar**  
 Beveled Mirror  
 Height: 4.25" Width: 18" Extends without Lamps: 3.25"  
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



**66449**  
**4 Light Bath Bar**  
 Beveled Mirror  
 Height: 4.25" Width: 24" Extends without Lamps: 3.25"  
 Use (4) Medium (E26) Base Lamps, 100 Watt Maximum



**66450**  
**6 Light Bath Bar**  
 Beveled Mirror  
 Height: 4.25" Width: 36"  
 Extends without Lamps: 3.25"  
 Use (6) Medium (E26) Base Lamps, 100 Watt Maximum

\*Fixture can be installed up or down



# Westinghouse

INNOVATION YOU CAN BE SURE OF



## INDOOR HANGING LIGHT FIXTURES

The perfect lighting fixture adds warm ambience and endless style to your home. From elegant chandeliers to sophisticated pendants, Westinghouse offers a variety of hanging fixtures that blend seamlessly with any home décor.

# HANGING LIGHT FIXTURE ASSORTMENT



**†63433**  
**Iron Hill**  
**4 Light Chandelier/Semi-Flush**  
*Oil Rubbed Bronze Finish with Highlights*  
 Height: 16.34" Diameter: 25.16" Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum

Height shown for Iron Hill fixtures is without lamps.



**†63450**  
**Iron Hill**  
**4 Light Chandelier/Semi-Flush**  
*Oil Rubbed Bronze Finish with Highlights and Metallic Bronze Interior*  
 Height: 16.34" Diameter: 25.16" Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**†63420**  
**Scholar**  
**4 Light Chandelier/Semi-Flush**  
*Oil Rubbed Bronze Finish with White Opal Glass*  
 Height: 20.08" Diameter: 23.86" Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



**63029**  
**5 Light Chandelier**  
*Amber Bronze Finish with Beige Fabric Shades*  
 Height: 30.12" Diameter: 25" Chain: 36" Cord: 60"  
 Use (5) Candelabra (E12) Base Lamps, 40 Watt Maximum



 **Westinghouse**  
**VINTAGE LAMPS**

Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.

†Fixture can be Chandelier or Semi-Flush Mount

## HANGING LIGHT FIXTURE ASSORTMENT

**63080****Ramsgate****5 Light Chandelier***Brushed Nickel Finish with Ice Glass**Height: 22" Diameter: 24" Chain: 36" Cord: 60"**Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*• **Replacement Glass #85006****63412****Karah****5 Light Chandelier***Brushed Nickel Finish with White Linen Glass**Height: 18" Diameter: 23" Chain: 36" Cord: 60"**Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*• **Replacement Glass #81003****63024****Ingram****4 Light Chandelier***Brushed Nickel Finish with Wavy White Glazed Glass**Height: 15.98" Diameter: 19.41" Chain: 36" Cord: 60"**Use (4) Medium (E26) Base Lamps, 60 Watt Maximum*• **Replacement Glass #85044****63441A****Hansen****5 Light Chandelier***Chrome Finish with White Linen Glass and Translucent Band**Height: 21.50" Diameter: 24.21"**Chain: 36" Cord: 60"**Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*• **Replacement Glass #81014****63441B****Hansen****5 Light Chandelier***Chrome Finish with White Linen Glass**Height: 21.50" Diameter: 24.21"**Chain: 36" Cord: 60"**Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*• **Replacement Glass #81016****63441C****Hansen****5 Light Chandelier***Chrome Finish with Glazed Ice Glass**Height: 21.50" Diameter: 25.28"**Chain: 36" Cord: 60"**Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*• **Replacement Glass #81018**• **Hand Blown Glass**• **Design Collection**





**63072**  
**Madori**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish with Amber Linen Glass*  
*Height: 27.72" Diameter: 23.82" Chain: 36" Cord: 60"*  
*Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*  
 • **Replacement Glass #81009**



**63071**  
**Malvern**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish with Smoldering Scavo Glass*  
*Height: 23.03" Diameter: 24.09"*  
*Chain: 36" Cord: 60"*  
*Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*  
**Replacement Glass #81017**



**63429**  
**Montrose**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish with Highlights and Mocha Scavo Glass*  
*Height: 27.44" Diameter: 23.50" Chain: 36" Cord: 60"*  
*Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*  
 • **Replacement Glass #81005**



▲ **63443A**  
**Ewing**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish with Amber Linen Glass*  
*Height: 21.50" Diameter: 25.35"*  
*Chain: 36" Cord: 60"*  
*Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*  
 • **Replacement Glass #81009**



▲ **63443B**  
**Ewing**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish with Amber Harvest Glass*  
*Height: 21.50" Diameter: 24.21"*  
*Chain: 36" Cord: 60"*  
*Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*  
 • **Replacement Glass #81015**



▲ **63443C**  
**Ewing**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish with Smoldering Scavo Glass*  
*Height: 21.50" Diameter: 25"*  
*Chain: 36" Cord: 60"*  
*Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*  
**Replacement Glass #81017**

• Hand Blown Glass  
 ▲ Design Collection

## HANGING LIGHT FIXTURE ASSORTMENT



**63057**  
**Dunmore**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish  
 with Frosted Glass*  
*Height: 23.50" Diameter: 23.50"*  
*Chain: 36" Cord: 60"*  
*Use (5) Medium (E26)*  
*Base Lamps, 60 Watt Maximum*  
 •Replacement Glass #85046



**63407**  
**Callan**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish  
 with Caramel Scavo Glass*  
*Height: 21.06" Diameter: 22.91"*  
*Chain: 36" Cord: 60"*  
*Use (5) Medium (E26)*  
*Base Lamps, 60 Watt Maximum*  
 Replacement Glass #81002



**63404**  
**Pacific Falls**  
**5 Light Chandelier**  
*Amber Bronze Finish with White Alabaster Glass*  
*Height: 24" Diameter: 24.72" Chain: 36" Cord: 60"*  
*Use (5) Medium (E26) Base Lamps, 60 Watt Maximum*  
 Replacement Glass #81000



**62235**  
**Trinity II**  
**5 Light Chandelier**  
*Oil Rubbed Bronze Finish  
 with Aged Alabaster Glass*  
*Height: 11" Width: 23"*  
*Chain: 36" Cord: 60"*  
*Use (5) Medium (E26) Base Lamps,*  
*60 Watt Maximum*



**62224**  
**Elena**  
**3 Light Chandelier**  
*Dark Bronze Finish  
 with Antique Amber Glass*  
*Height: 21.25" Width: 19.13"*  
*Chain: 36" Cord: 120"*  
*Use (3) Medium (E26) Base Lamps,*  
*60 Watt Maximum*

•Hand Blown Glass

**63001**  
**Harwell**  
**5 Light Chandelier**  
 Brushed Nickel Finish  
 with White Opal Glass  
 Height: 16.24" Diameter: 22.64"  
 Chain: 36" Cord: 60"  
 Use (5) Medium (E26)  
 Base Lamps,  
 60 Watt Maximum  
**Replacement Glass #85043**



**63042**  
**Harwell**  
**5 Light Chandelier**  
 Amber Bronze Finish  
 with White Opal Glass  
 Height: 16.24" Diameter: 22.64"  
 Chain: 36" Cord: 60"  
 Use (5) Medium (E26)  
 Base Lamps,  
 60 Watt Maximum  
**Replacement Glass #85043**



**63436B**  
**Wilkes**  
**4 Light Chandelier**  
 Gun Metal Finish with White Linen Glass  
 Height: 15.94" Diameter: 20.04" Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum  
**Replacement Glass #81013**



**63436A**  
**Wilkes**  
**4 Light Chandelier**  
 Gun Metal Finish with Lunar Weave Glass  
 Height: 15.94" Diameter: 20.04" Chain: 36" Cord: 60"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum  
**Replacement Glass #81006**



**62275**  
**Sylvestre**  
**3 Light Chandelier**  
 Brushed Nickel Finish  
 with Frosted Seeded Glass  
 Height: 17.63" Diameter: 18.25"  
 Chain: 36" Cord: 120"  
 Use (3) Medium (E26) Base Lamps,  
 60 Watt Maximum



**62274**  
**Sylvestre**  
**5 Light Chandelier**  
 Brushed Nickel Finish  
 with Frosted Seeded Glass  
 Height: 18.50" Diameter: 20.63"  
 Chain: 36" Cord: 120"  
 Use (5) Medium (E26) Base  
 Lamps, 60 Watt Maximum



• Hand Blown Glass  
 ▲ Design Collection

# HANGING LIGHT FIXTURE ASSORTMENT



Highlight Detail Shown

**63037**

**Isadora**

**3 Light Chandelier**

*Oil Rubbed Bronze Finish with Highlights*

*Height: 18.75" Diameter: 12.75"*

*Chain: 36" Cord: 60"*

*Use (3) Candelabra*

*(E12) Base Lamps, 40 Watt Maximum*



**63038**

**Isadora**

**3 Light Chandelier**

*Brushed Nickel Finish*

*Height: 18.75" Diameter: 12.75"*

*Chain: 36" Cord: 60"*

*Use (3) Candelabra*

*(E12) Base Lamps, 40 Watt Maximum*



**63419**

**Stella Mira**

**3 Light Pendant**

*Brushed Nickel Finish*

*Height: 17.28"*

*Diameter: 15.04"*

*Chain: 36" Cord: 60"*

*Use (3) Candelabra (E12)*

*Base Lamps, 40 Watt Maximum*



**63418**

**Stella Mira**

**3 Light Pendant**

*Oil Rubbed Bronze Finish with Highlights*

*Height: 17.28"*

*Diameter: 15.04"*

*Chain: 36" Cord: 60"*

*Use (3) Candelabra (E12)*

*Base Lamps, 40 Watt Maximum*



**63033**

**Brixton**

**6 Light Chandelier**

*Oil Rubbed Bronze Finish with Highlights*

*Height: 18.03" Diameter: 25"*

*Chain: 36" Cord: 60"*

*Use (6) Candelabra (E12)*

*Base Lamps, 40 Watt Maximum*



Highlight Detail Shown



**63031**

**Brixton**

**6 Light Chandelier**

*Brushed Nickel Finish*

*Height: 18.03" Diameter: 25"*

*Chain: 36" Cord: 60"*

*Use (6) Candelabra (E12)*

*Base Lamps, 40 Watt Maximum*



Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.








**†63403**  
**Pacific Falls**  
**2 Light Pendant/Semi-Flush**  
*Amber Bronze Finish with White Alabaster Glass*  
*Height: 13.86" Diameter: 13.98"*  
*Chain: 36" Cord: 60"*  
*Use (2) Medium (E26) Base Lamps, 60 Watt Maximum*



**†63044**  
**Harwell**  
**3 Light Pendant/Semi-Flush**  
*Amber Bronze Finish with Frosted Glass*  
*Height: 17.87" Diameter: 16.06"*  
*Chain: 36" Cord: 60"*  
*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*



**†63054**  
**Harwell**  
**3 Light Pendant/Semi-Flush**  
*Brushed Nickel Finish with Frosted Glass*  
*Height: 17.87" Diameter: 16.06"*  
*Chain: 36" Cord: 60"*  
*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*




**63060**  
**Dunmore**  
**1 Light Pendant**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
*Height: 13.46" Diameter: 15.20"*  
*Chain: 36" Cord: 60"*  
*Use (1) Medium (E26) Base Lamp, 60 Watt Maximum*



**†63417**  
**Packard**  
**2 Light Pendant/Semi-Flush**  
*Amber Bronze Finish with Beige Fabric Shade and Frosted Glass Panel*  
*Height: 17.60" Diameter: 14" Chain: 36" Cord: 60"*  
*Use (2) Medium (E26) Base Lamps, 60 Watt Maximum*

**63059**  
**Dunmore**  
**2 Light Island Pendant**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
*Height: 18.54" Width: 37"*  
*Chain: 36" Cord: 60"*  
*Use (2) Medium (E26) Base Lamps, 60 Watt Maximum*  
**Replacement Glass #85046**



**63058**  
**Dunmore**  
**3 Light Pendant**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
*Height: 23.58" Diameter: 16.57"*  
*Chain: 36" Cord: 60"*  
*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*



†Fixture can be Pendant or Semi-Flush Mount

# HANGING LIGHT FIXTURE ASSORTMENT



**DIMMABLE**  
**LED**

**1 Light LED Mini Pendant**  
Boswell  
Oil Rubbed Bronze Finish  
with Highlights and Prismatic Lens  
Height: 41.34" Diameter: 8.75"

**63082A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63082B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE**  
**LED**

**1 Light LED Mini Pendant**  
Boswell  
Chrome Finish  
with Prismatic Lens  
Height: 41.34" Diameter: 8.75"

▲ **63083A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63083B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE**  
**LED**

**1 Light LED Mini Pendant**  
Boswell  
Washed Copper Finish  
with Prismatic Lens  
Height: 41.34" Diameter: 8.75"

**63084A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63084B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE**  
**LED**

**1 Light LED Pendant**  
Oil Rubbed Bronze Finish  
with Highlights and Prismatic Lens  
Height: 43.54" Diameter: 10.63"

▲ **63087A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63087B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE**  
**LED**

**1 Light LED Pendant**  
Chrome Finish  
with Prismatic Lens  
Height: 43.54" Diameter: 10.63"

**63085A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63085B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp



**DIMMABLE**  
**LED**

**1 Light LED Pendant**  
Washed Copper Finish  
with Prismatic Lens  
Height: 43.54" Diameter: 10.63"

▲ **63086A**  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp

▲ **63086B**  
Includes (1) Medium (E26) Base,  
11 Watt Omni A21 LED Lamp

Boswell Collection includes (3) 9.5" long rods. Install 1, 2, or 3 rods for customized lengths.

## DIMMABLE LED LIGHT SOURCE SPECIFICATIONS

Model Type	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Avg. Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
Model A	1	9	60	3000 (Warm White)	800	80	25000	22.8	\$1.08
Model B	1	11	75	3000 (Warm White)	1100	80	25000	22.8	\$1.32

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

▲ Design Collection



**63096**  
**1 Light Pendant**  
 Hammered  
 Brushed Nickel Finish  
 Height: 38.50" Diameter: 10.24"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum  
 Includes (3) 9.5" long rods.  
 Install 1, 2, or 3 rods for  
 customized lengths.



**63099**  
**1 Light Pendant**  
 Hammered  
 Oil Rubbed Bronze Finish  
 Height: 38.50" Diameter: 10.24"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum  
 Includes (3) 9.5" long rods.  
 Install 1, 2, or 3 rods for  
 customized lengths.




**63455**  
**1 Light Mini Pendant**  
 Hammered Brushed  
 Nickel Finish  
 Height: 41.38" Diameter: 7.75"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum




**63456**  
**1 Light Mini Pendant**  
 Hammered Oil Rubbed Bronze  
 Finish with Highlights  
 Height: 41.38" Diameter: 7.75"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum

INTEGRATED  
**LED**




**64010**  
**1 Light LED  
 Pendant**  
 Black Finish  
 with Chrome Cage  
 Height: 61.50"  
 Diameter: 12.13"  
 Adjustable Cord: 50"  
 Includes 13 Watt  
 Integrated LED


INTEGRATED  
 DIMMABLE  
**LED**



**63079**  
 Cava  
**1 Light LED  
 Mini Pendant**  
 Chrome Finish with  
 Bubble Glass  
 Height: 61.05"  
 Diameter: 4.96"  
 Adjustable Cord: 50"  
 Includes 8 Watt  
 Integrated LED



**63447**  
 Iron Hill  
**1 Light Pendant**  
 Oil Rubbed Bronze Finish  
 with Highlights and  
 Metallic Bronze Interior  
 Height: 57.15"  
 Diameter: 12"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26)  
 Base Lamp,  
 60 Watt Maximum



**63090**  
**1 Light Pendant**  
 Matte Black and  
 Washed Copper Finish  
 Height: 57.87"  
 Diameter: 10.24"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26)  
 Base Lamp,  
 60 Watt Maximum

Add Westinghouse Filament LED or  
 Timeless lamps for the vintage look you want.

 **Westinghouse**  
**VINTAGE LAMPS**



**LED LIGHT SOURCE SPECIFICATIONS**

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
63079	*	8	40	3000 (Warm White)	450	80	25000	22.8	\$0.96
64010	*	16	75	3000 (Warm White)	900	80	30000	27.3	\$1.93

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).  
 \* Integrated LED Light Source

\*\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# HANGING LIGHT FIXTURE ASSORTMENT



**63460**  
**1 Light Mini Pendant with Turn Knob**  
*Oil Rubbed Bronze Finish with Clear Glass*  
 Height: 60"  
 Diameter: 9"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63466**  
**1 Light Mini Pendant**  
*Antique Brass Finish with Diamond Cut Clear Glass*  
 Height: 60.87"  
 Diameter: 5.90"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63465**  
**1 Light Mini Pendant with Turn Knob**  
*Oil Rubbed Bronze Finish with Frosted Opal Glass*  
 Height: 60.24"  
 Diameter: 8.74"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63464**  
**1 Light Mini Pendant with Turn Knob**  
*Antique Brass Finish with White Opal Glass*  
 Height: 60.24"  
 Diameter: 8.74"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63461**  
**1 Light Mini Pendant with Turn Knob**  
*Antique Brass Finish with Frosted Opal Glass*  
 Height: 60"  
 Diameter: 9"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63463**  
**1 Light Mini Pendant**  
*Matte Black Finish with Frosted Opal Glass*  
 Height: 60.24"  
 Diameter: 8.66"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**63462**  
**1 Light Mini Pendant**  
*Oil Rubbed Bronze Finish with White Opal Glass*  
 Height: 60.24"  
 Diameter: 8.66"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.









**61007**  
**1 Light**  
**Mini Pendant**  
 Brushed Nickel Finish with Clear Seeded Glass  
 Height: 60"  
 Diameter: 7"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**61008**  
**1 Light**  
**Mini Pendant**  
 Oil Rubbed Bronze Finish with Clear Seeded Glass  
 Height: 60"  
 Diameter: 7"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**61026**  
**1 Light**  
**Mini Pendant**  
 Oil Rubbed Bronze Finish with Clear Glass  
 Height: 60.25"  
 Diameter: 7.50"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**63091**  
**1 Light**  
**Mini Pendant**  
 Brushed Nickel Finish with Clear Crackle Glass  
 Height: 63.5"  
 Diameter: 7.50"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63092**  
**1 Light**  
**Mini Pendant**  
 Brushed Nickel Finish with Clear Crackle Glass  
 Height: 60"  
 Diameter: 6"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63458**  
**1 Light**  
**Pendant**  
 Chrome Finish with Clear Glass  
 Height: 58.88"  
 Diameter: 9.41"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63457**  
**1 Light**  
**Mini Pendant**  
 Brushed Nickel Finish with Clear Glass  
 Height: 60.23"  
 Diameter: 7.48"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63093**  
**1 Light**  
**Mini Pendant**  
 Matte Black Finish with Frosted Opal Glass  
 Height: 62.70"  
 Diameter: 7"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**63095**  
**1 Light**  
**Mini Pendant**  
 Matte Black Finish with Frosted Opal Glass  
 Height: 62.70"  
 Diameter: 7"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.




# HANGING LIGHT FIXTURE ASSORTMENT



**63459**  
**1 Light**  
**Mini Pendant**  
 Matte Black Finish  
 with Matte Black  
 and Amber Glass  
 Height: 65.55"  
 Diameter: 7.87"  
 Adjustable Cord: 50"  
 Use (1) Medium  
 (E26) Base Lamp,  
 60 Watt Maximum



**62052**  
**1 Light**  
**Mini Pendant**  
 Oil Rubbed  
 Bronze Finish  
 with Amber Glass  
 Height: 60"  
 Diameter: 6"  
 Adjustable Cord: 50"  
 Use (1) Medium  
 (E26) Base Lamp,  
 60 Watt Maximum



**62053**  
**1 Light**  
**Mini Pendant**  
 Copper Finish  
 with Amber Glass  
 Height: 61.5"  
 Diameter: 8"  
 Adjustable Cord: 50"  
 Use (1) Medium  
 (E26) Base Lamp,  
 60 Watt Maximum




**62054**  
**1 Light**  
**Mini Pendant**  
 Copper Finish  
 with Amber Glass  
 Height: 61"  
 Diameter: 9"  
 Adjustable Cord: 50"  
 Use (1) Medium  
 (E26) Base Lamp,  
 60 Watt Maximum



**New!**

**63235**  
**1 Light**  
**Mini Pendant**  
**with Turn Knob**  
 Brushed Nickel  
 Finish with Cage Shade  
 Height: 62.50"  
 Diameter: 6"  
 Adjustable Cord: 50"  
 Use (1) Medium  
 (E26) Base Lamp,  
 60 Watt Maximum




**New!**

**63236**  
**1 Light**  
**Mini Pendant**  
**with Turn Knob**  
 Oil Rubbed Bronze  
 Finish with Cage Shade  
 Height: 62.50"  
 Diameter: 6"  
 Adjustable Cord: 50"  
 Use (1) Medium  
 (E26) Base Lamp,  
 60 Watt Maximum




**62051**  
**1 Light**  
**Pendant**  
 Matte Black Finish  
 with Metal Cage  
 and Frosted White Glass  
 Height: 68"  
 Diameter: 11.80"  
 Adjustable Cord: 50"  
 Use (1) Medium  
 (E26) Base Lamp,  
 60 Watt Maximum




**61006**  
**1 Light**  
**Mini Pendant**  
 Oil Rubbed Bronze  
 Finish with Cage Shade  
 Height: 59"  
 Diameter: 6"  
 Adjustable Cord: 50"  
 Use (1) Medium  
 (E26) Base Lamp,  
 60 Watt Maximum

Add Westinghouse Filament LED or  
 Timeless lamps for the vintage look you want.







**63452**  
**1 Light Pendant**  
*Oil Rubbed Bronze Finish with Cage Shade*  
 Height: 42.50"  
 Diameter: 9.84"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum  
 Includes (3) 9.5" long rods. Install 1, 2, or 3 rods for customized lengths.




**63451**  
**1 Light Pendant**  
*Matte Black Finish with Cage Shade*  
 Height: 61.42"  
 Diameter: 10.24"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**63453**  
**1 Light Mini Pendant**  
*Brushed Nickel Finish with Mesh Shade*  
 Height: 62.60"  
 Diameter: 6"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**63454**  
**1 Light Mini Pendant**  
*Oil Rubbed Bronze Finish with Mesh Shade*  
 Height: 62.60"  
 Diameter: 6"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**61011**  
**1 Light Mini Pendant**  
*Brushed Nickel Finish with White Glass*  
 Height: 57.50"  
 Diameter: 8"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum




**61009**  
**1 Light Mini Pendant**  
*Black Finish with Black Glass*  
 Height: 60.50"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**61013**  
**1 Light Mini Pendant**  
*Brushed Nickel Finish with Perforated Metal Shade*  
 Height: 60"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**61012**  
**1 Light Mini Pendant**  
*Brushed Nickel Finish with Perforated Metal Shade*  
 Height: 59"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum









**60004**  
**1 Light Mini Pendant**  
*Oil Rubbed Bronze Finish with Amber Glass*  
 Height: 58.90"  
 Diameter: 6.70"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum


Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.




## HANGING LIGHT FIXTURE ASSORTMENT

**63007****Harwell****1 Light****Mini Pendant***Brushed Nickel Finish  
with White Opal Glass**Height: 37.71" Diameter: 6.61"**Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum**Includes (3) 9.5" long rods.**Install 1, 2, or 3 rods for  
customized lengths.***63047****Harwell****1 Light****Mini Pendant***Amber Bronze Finish  
with White Opal Glass**Height: 37.71" Diameter: 6.61"**Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum**Includes (3) 9.5" long rods.**Install 1, 2, or 3 rods for  
customized lengths.***69231****Winchester****1 Light****Pendant***Brushed Nickel Finish  
with Frosted White Alabaster Glass**Height: 38" Diameter: 9.50"**Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum**Includes (3) 9.5" long rods.**Install 1, 2, or 3 rods for  
customized lengths.***63061****Dunmore****1 Light****Mini Pendant***Oil Rubbed Bronze Finish  
with Frosted Glass**Height: 37.68"**Diameter: 6.14"**Use (1) Medium**(E26) Base Lamp,  
60 Watt Maximum**Includes (3) 9.5" long rods.**Install 1, 2, or 3 rods for  
customized lengths.***62201****Wensley****1 Light****Mini Pendant***Oil Rubbed Bronze Finish  
with White Alabaster Glass**Height: 37.25"**Diameter: 5.88"**Use (1) Medium**(E26) Base Lamp,  
60 Watt Maximum**Includes (3) 9.5" long rods.**Install 1, 2, or 3 rods for  
customized lengths.***63431****Montrose****1 Light****Mini Pendant***Oil Rubbed Bronze Finish  
with Highlights and  
Mocha Scavo Glass**Height: 40.08"**Diameter: 6.38"**Use (1) Medium**(E26) Base Lamp,  
60 Watt Maximum**Includes (3) 9.5" long rods.**Install 1, 2, or 3 rods for  
customized lengths.***63402****Pacific Falls****1 Light****Mini Pendant***Amber Bronze Finish  
with White Alabaster Glass**Height: 42.20"**Diameter: 7"**Use (1) Medium**(E26) Base Lamp,  
60 Watt Maximum**Includes (3) 11.5" long rods.**Install 1, 2, or 3 rods for  
customized lengths.*






**67384**  
**1 Light**  
**Mini Pendant**  
*Oil Rubbed Bronze Finish*  
*with Fire Storm Glass Shade*  
*Height: 59.50"*  
*Diameter: 5"*  
*Adjustable Cord: 50"*  
*Use (1) Medium*  
*(E26) Base Lamp,*  
*60 Watt Maximum*



**61017**  
**1 Light**  
**Mini Pendant**  
*Red Finish*  
*with Metal Shade*  
*Height: 58.25"*  
*Diameter: 7"*  
*Adjustable Cord: 50"*  
*Use (1) Medium*  
*(E26) Base Lamp,*  
*60 Watt Maximum*



**61019**  
**1 Light**  
**Mini Pendant**  
*Yellow Finish*  
*with Metal Shade*  
*Height: 58.25"*  
*Diameter: 7"*  
*Adjustable Cord: 50"*  
*Use (1) Medium*  
*(E26) Base Lamp,*  
*60 Watt Maximum*



**66198**  
**1 Light**  
**Pendant**  
*White Finish*  
*Height: 8.5"*  
*Diameter: 15.50"*  
*Adjustable Cord: 48"*  
*Use (1) Medium (E26) Base Lamp,*  
*100 Watt Maximum*



**63004**  
**Harwell**  
**1 Light Pendant**  
*Brushed Nickel Finish*  
*with Frosted Glass*  
*Height: 9.65" Diameter: 15.91"*  
*Chain: 36" Cord: 60"*  
*Use (1) Medium (E26) Base Lamp,*  
*60 Watt Maximum*



**63043**  
**Harwell**  
**1 Light Pendant**  
*Amber Bronze Finish*  
*with Frosted Glass*  
*Height: 9.65" Diameter: 15.91"*  
*Chain: 36" Cord: 60"*  
*Use (1) Medium (E26) Base Lamp,*  
*60 Watt Maximum*



# Westinghouse

INNOVATION YOU CAN BE SURE OF




## DesignerYou® RETRO PENDANTS & SHADES

Customize our retro pendants with vintage-style shades to create distinctive period-style pendants. Old World details are modernized with fresh, exciting shade designs that add warmth and a touch of nostalgia to any space.



**\*61031**  
**1 Light Retro Mini Pendant with Turn Knob**  
*Antique Brass Finish*  
 Height: 55"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**\*61032**  
**1 Light Retro Mini Pendant**  
*Oil Rubbed Bronze Finish*  
 Height: 55"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**†81022**  
**Champagne Glass Wide Rippled Shade with Adapters**  
 Fitter: 2.25"  
 Height: 5.51"  
 Diameter: 7.75"



**†81025**  
**White Opal Schoolhouse Shade with Adapters**  
 Fitter: 2.25"  
 Height: 7.01"  
 Diameter: 10"



**†81024**  
**Diamond Cut Clear Glass Globe with Adapters**  
 Fitter: 2.25"  
 Height: 8.27"  
 Diameter: 7.68"

\*Ideal for use with Retro and neckless shades.

†Adapters included to allow shades to fit 2¼" fitter pendants. (Antique Brass and Oil Rubbed Bronze Finishes)

# RETRO ASSORTMENT



• **81020**  
**Champagne Glass  
 Rippled Cone Shade**  
*Fitter: 2.25"*  
*Height: 7"*  
*Diameter: 5"*



• **81021**  
**Clear Glass  
 Open Teardrop Shade**  
*Fitter: 2.25"*  
*Height: 7"*  
*Diameter: 7.50"*



**81019**  
**Matte Black Globe  
 Cage Shade**  
*Fitter: 2.25"*  
*Height: 7"*  
*Diameter: 8"*



**81023**  
**Matte Black Angled Bell  
 Cage Shade**  
*Fitter: 2.25"*  
*Height: 6.50"*  
*Diameter: 7.60"*



**85031**  
**Brushed Nickel Finish  
 Cage Shade with  
 Closed Bottom**  
*Fitter: 2.25"*  
*Height: 8"*  
*Diameter: 6.75"*

**New!**



**85052**  
**Brushed Nickel Finish  
 Cage Shade with  
 Latched Bottom**  
*Fitter: 2.25"*  
*Height: 8.19"*  
*Diameter: 6"*



**85033**  
**Oil Rubbed Bronze Finish  
 Cage Shade with  
 Closed Bottom**  
*Fitter: 2.25"*  
*Height: 8"*  
*Diameter: 6.75"*

**New!**



**85051**  
**Oil Rubbed Bronze Finish  
 Cage Shade with  
 Latched Bottom**  
*Fitter: 2.25"*  
*Height: 8.19"*  
*Diameter: 6"*



**85036**  
**Brushed Nickel Finish  
 Cage Shade with  
 Open Bottom**  
*Fitter: 2.25"*  
*Height: 6.25"*  
*Diameter: 5.75"*



**85038**  
**Oil Rubbed Bronze Finish  
 Cage Shade with  
 Open Bottom**  
*Fitter: 2.25"*  
*Height: 6.25"*  
*Diameter: 5.75"*




**Westinghouse**  
**VINTAGE LAMPS**

Add Westinghouse Filament LED or  
 Timeless lamps for the vintage look you want.



# Westinghouse

INNOVATION YOU CAN BE SURE OF



INTEGRATED  
DIMMABLE  
LED

**61030**  
**1 Light**  
**LED Mini Pendant**

*Brushed Nickel Finish*

*Height: 57.28"*

*Diameter: 5"*

*Adjustable Cord: 50"*

*Includes 9 Watt*

*Integrated LED*

**INTEGRATED  
DIMMABLE  
LED LIGHT SOURCE  
SPECIFICATIONS**

Total Energy Used (Watts)	9
Equivalent Incandescent Wattage	60
Light Appearance (Kelvin)	2700K (Warm White)
Total Lumens	750
Avg. Rated Hours	25000
CRI	80
Life in Years*	22.8
Total Est. Yearly Energy Cost**	\$1.08

\*Based on 3hrs./day

\*\*Based on 3hrs./day 11¢/kWh

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

## DesignerYou® YOUR LIGHT, YOUR CHOICE...

Completely customizable fixtures inspire creativity for quick and easy home upgrades. Pair stylish glass and metal 2¼" fitter shades with sleek lighting fixtures or transform existing lighting with designer glass. It's as easy as 1-2-3.



# CHOOSE YOUR FIXTURE AND FINISH




**85718**  
**1 Light Mini Pendant**  
 Chrome Finish  
 Height: 55"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**70287**  
**1 Light Mini Pendant**  
 Antique Brass Finish  
 Height: 55"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**70285**  
**1 Light Mini Pendant**  
 Oil Rubbed Bronze Finish  
 Height: 55"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**70286**  
**1 Light Mini Pendant**  
 White Finish  
 Height: 55"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum




**70284**  
**1 Light Mini Pendant**  
 Brushed Nickel Finish  
 Height: 55"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**61024**  
**1 Light Mini Pendant**  
 Oil Rubbed Bronze Finish  
 Height: 53.38"  
 Diameter: 5"  
 Adjustable Cord: 50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum

## RENOVATE AND UPDATE...

You can transform existing recessed lighting into a pendant or other light fixture with the Recessed Light Converter!



**01011**  
**Recessed Light Converter**

- Quick and easy home upgrade with no remodeling
- Adjusts to any recessed can size between 4"- 6" diameter
- Works with existing recessed cans that use medium base lamps
- 50 lb. maximum load rating



PATENTED TECHNOLOGY | US PATENT NO. 9,496,699

# CHOOSE YOUR FIXTURE AND FINISH

**63013**  
**3 Light**  
**Mini Pendant**

*Oil Rubbed Bronze Finish*

*Height: 55"*

*Width: 23.50"*

*Depth: 4.50"*

*Adjustable Cord: 50"*

*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*



**63012**  
**3 Light**  
**Mini Pendant**

*Brushed Nickel Finish*


*Height: 55"*

*Width: 23.50"*

*Depth: 4.50"*

*Adjustable Cord: 50"*

*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*



**\*67480**  
**3 Light Wall**

*Brushed Nickel Finish*

*Height: 5.88" Width: 22.63" Extends: 8.63"*

*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*



**\*67485**  
**3 Light Wall**

*Oil Rubbed Bronze Finish*

*Height: 5.98" Width: 21.10" Extends: 5.63"*

*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*



**\*67482**  
**3 Light Wall**

*Brushed Nickel Finish*

*Height: 5.98" Width: 21.10" Extends: 5.63"*

*Use (3) Medium (E26) Base Lamps, 60 Watt Maximum*



**\*Fixture can be installed up or down**



**\*63002**  
**1 Light Wall**  
 Brushed Nickel Finish  
 Height: 9"  
 Width: 4"  
 Extends: 6.50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**\*63000**  
**1 Light Wall**  
 Oil Rubbed Bronze Finish  
 Height: 9"  
 Width: 4"  
 Extends: 6.50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**\*63005**  
**2 Light Wall**  
 Brushed Nickel Finish  
 Height: 6.50" Width: 11" Extends: 5"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63003**  
**2 Light Wall**  
 Oil Rubbed Bronze Finish  
 Height: 6.50" Width: 11" Extends: 5"  
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63008**  
**3 Light Wall**  
 Brushed Nickel Finish  
 Height: 7" Width: 19.50" Extends: 6.50"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63006**  
**3 Light Wall**  
 Oil Rubbed Bronze Finish  
 Height: 7" Width: 19.50" Extends: 6.50"  
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



**\*63009**  
**4 Light Wall**  
 Oil Rubbed Bronze Finish  
 Height: 7" Width: 24" Extends: 6.50"  
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum

\*Fixture can be installed up or down

# CHOOSE YOUR SHADE

Versatile glass shades are the perfect upgrade for pendants, vanity fixtures and ceiling fans.



**New!**

• **85004**  
**White Linen**  
**Cube Shade**  
*Fitter: 2.25"*  
*Height: 7"*  
*Width: 3.94"*



• **85044**  
**Wavy White**  
**Glazed Cube**  
**Shade**  
*Fitter: 2.25"*  
*Height: 6"*  
*Width: 3.75"*



• **85045**  
**Rippled White Glazed**  
**Rectangular Shade**  
*Fitter: 2.25"*  
*Height: 6"*  
*Width: 6"*  
*Depth: 4"*



**81000**  
**White Alabaster**  
**Flared Bell Shade**  
*Fitter: 2.25"*  
*Height: 4.33"*  
*Diameter: 6.97"*



**81002**  
**Caramel Scavo**  
**Bell Shade**  
*Fitter: 2.25"*  
*Height: 4.61"*  
*Diameter: 6.06"*



• **85043**  
**White Opal**  
**Bell Shade**  
*Fitter: 2.25"*  
*Height: 4.88"*  
*Diameter: 6.61"*



**85047**  
**Frosted**  
**Dome Shade**  
*Fitter: 2.25"*  
*Height: 4.69"*  
*Diameter: 5.79"*



**81017**  
**Smoldering Scavo**  
**Cone Shade**  
*Fitter: 2.25"*  
*Height: 5.60"*  
*Diameter: 4.75"*



• **81006**  
**Lunar Weave**  
**Flared Cube Shade**  
*Fitter: 2.25"*  
*Height: 5.27"*  
*Width: 5"*



• **81013**  
**White Linen**  
**Flared Cube Shade**  
*Fitter: 2.25"*  
*Height: 5.27"*  
*Width: 5"*



• **81009**  
**Amber Linen**  
**Flared Cube Shade**  
*Fitter: 2.25"*  
*Height: 5.27"*  
*Width: 5"*



• **81014**  
**White Linen**  
**Cylinder Shade with**  
**Translucent Band**  
*Fitter: 2.25"*  
*Height: 5.12"*  
*Diameter: 3.94"*



• **81015**  
**Amber Harvest**  
**Cylinder Shade**  
*Fitter: 2.25"*  
*Height: 5.12"*  
*Diameter: 3.94"*



• **81016**  
**White Linen**  
**Cylinder Shade**  
*Fitter: 2.25"*  
*Height: 5.12"*  
*Diameter: 3.94"*



• **85006**  
**Ice**  
**Cylinder Shade**  
*Fitter: 2.25"*  
*Height: 5.15"*  
*Diameter: 4"*


•Hand Blown Glass





**81018**  
**Glazed Ice**  
**Cubic Dome Shade**

Fitter: 2.25"  
 Height: 6"  
 Width: 5"



**85012**  
**Charcoal Swirl**  
**Cubic Dome Shade**

Fitter: 2.25"  
 Height: 5.50"  
 Width: 5.50"

**New!**



**85003**  
**White and Clear**  
**Etched Cylinder Shade**

Fitter: 2.25"  
 Height: 7.88"  
 Diameter: 4.80"



**85005**  
**White Alabaster**  
**Large Cylinder Shade**

Fitter: 2.25"  
 Height: 7.88"  
 Diameter: 4.63"



**85046**  
**Frosted Flared**  
**Cone Shade**

Fitter: 2.25"  
 Height: 5.32"  
 Diameter: 6.14"



**81003**  
**White Linen**  
**Barrel Shade**

Fitter: 2.25"  
 Height: 5.30"  
 Diameter: 4.92"



**81004**  
**Aged Amber Scavo**  
**Barrel Shade**

Fitter: 2.25"  
 Height: 5.30"  
 Diameter: 4.92"



**81407**  
**Garden Moss Shade**

Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 4.50"



**81310**  
**Giraffe Spot Shade**

Fitter: 2.25"  
 Height: 5.38"  
 Diameter: 4.50"



**81311**  
**Fire Pit Shade**

Fitter: 2.25"  
 Height: 5.38"  
 Diameter: 4.50"



**81409**  
**Charcoal Swirl Shade**

Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 4.85"



**81400**  
**Wildfire**  
**Cylinder Shade**

Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 4.75"



**81404**  
**Marble**  
**Cylinder Shade**

Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 4.75"



**85701**  
**Ice**  
**Cylinder Shade**

Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 4.75"



**85702**  
**Brushed Nickel**  
**Perforated Metal Shade**

Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 5"

•Hand Blown Glass

# CHOOSE YOUR SHADE

Versatile glass shades are the perfect upgrade for pendants, vanity fixtures and ceiling fans.



**New!**

**85050**  
**Crystal Jewel**  
**Elongated Shade**  
 Fitter: 2.25"  
 Height: 10"  
 Diameter: 6"



**85730**  
**Fire Pit**  
**Long Shade**  
 Fitter: 2.25"  
 Height: 8.50"  
 Diameter: 4.5"



**85724**  
**Lunar Weave**  
**Long Shade**  
 Fitter: 2.25"  
 Height: 7.75"  
 Diameter: 4.75"



**81005**  
**Mocha Scavo**  
**Bell Shade with**  
**Raised Band**  
 Fitter: 2.25"  
 Height: 5.70"  
 Diameter: 5"



**81405**  
**Van Gogh**  
**Shade**  
 Fitter: 2.25"  
 Height: 6.25"  
 Diameter: 4.38"



**81413**  
**Chili Pepper**  
**Shade**  
 Fitter: 2.25"  
 Height: 6.25"  
 Diameter: 4.38"



**81364**  
**Temptress**  
**Red Shade**  
 Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 4"



**81427**  
**Spice Swirl**  
**Shade**  
 Fitter: 2.25"  
 Height: 5.75"  
 Diameter: 4.63"



**81410**  
**Chocolate Drizzle**  
**Shade**  
 Fitter: 2.25"  
 Height: 6.38"  
 Diameter: 4.38"



**81412**  
**Lunar Weave**  
**Shade**  
 Fitter: 2.25"  
 Height: 6"  
 Diameter: 5.38"



**85722**  
**White Opal**  
**Fluted Shade**  
 Fitter: 2.25"  
 Height: 5.50"  
 Diameter: 4.75"



**81414**  
**Linen Globe**  
 Fitter: 2.25"  
 Height: 4.88"  
 Diameter: 5.25"



•81353  
**Clear and White  
 Design Bell**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5"



•81315  
**Clear with Black  
 Rope Shade**  
 Fitter: 2.25"  
 Height: 5.75"  
 Diameter: 4.63"



•81314  
**Clear with White  
 Rope Shade**  
 Fitter: 2.25"  
 Height: 5.75"  
 Diameter: 4.63"



81277  
**Beveled  
 Clear Glass Bell**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 4.88"



•81095  
**Clear  
 Seeded Bell**  
 Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 4.81"



81098  
**Milky  
 Scavo Bell**  
 Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 5.50"



81279  
**Milky  
 Scavo Bell**  
 Fitter: 2.25"  
 Height: 5.13"  
 Diameter: 5.13"



•81363  
**Burnt Umber  
 Swirl Bell**  
 Fitter: 2.25"  
 Height: 4.81"  
 Diameter: 5.38"



81265  
**Hand-Painted  
 Leaf Design Bell**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5.38"



81272  
**Milky Scavo Bell**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5.38"



81391  
**Antique  
 Smolder Bell**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5.25"



81167  
**Brown Swirl Bell**  
 Fitter: 2.25"  
 Height: 5.13"  
 Diameter: 5.88"



81119  
**Licorice Marbleized Bell**  
 Fitter: 2.25"  
 Height: 4.50"  
 Diameter: 4.75"



81422  
**Brown Marbleized Bell**  
 Fitter: 2.25"  
 Height: 4.65"  
 Diameter: 5.40"



81257  
**Sandy Fluted Bell**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5.50"

# CHOOSE YOUR SHADE

Versatile glass shades are the perfect upgrade for pendants, vanity fixtures and ceiling fans.



**81051**  
**Frosted Etched  
 Bell Shade**  
*Fitter: 2.25"*  
*Height: 4.50"*  
*Diameter: 4.75"*



**81227**  
**White Opal  
 Bell Shade**  
*Fitter: 2.25"*  
*Height: 4.75"*  
*Diameter: 4.75"*



**81253**  
**Frosted  
 Bell Shade with Clear  
 Square Design**  
*Fitter: 2.25"*  
*Height: 4.63"*  
*Diameter: 5.38"*



**81270**  
**Frosted and Clear  
 Cross Shade**  
*Fitter: 2.25"*  
*Height: 5.25"*  
*Diameter: 5"*



**81097**  
**Frosted Pleated  
 Shade**  
*Fitter: 2.25"*  
*Height: 5"*  
*Diameter: 4.25"*



**81356**  
**Tortoise Bell  
 Shade**  
*Fitter: 2.25"*  
*Height: 5.38"*  
*Diameter: 4.75"*



**81121**  
**Square  
 Tiffany Shade**  
*Fitter: 2.25"*  
*Height: 5.13"*  
*Diameter: 4.75"*



**81365**  
**Parchment  
 Leaf Shade**  
*Fitter: 2.25"*  
*Height: 4.50"*  
*Diameter: 6"*



**81120**  
**Cappuccino Swirl  
 Shade**  
*Fitter: 2.25"*  
*Height: 4.25"*  
*Diameter: 6.88"*



**81333**  
**Honey Swirl  
 Scavo Shade**  
*Fitter: 2.25"*  
*Height: 4.38"*  
*Diameter: 6.88"*



**81382**  
**Linen Pendant  
 Shade**  
*Fitter: 2.25"*  
*Height: 5"*  
*Diameter: 7.75"*



# SHELF DISPLAYS



Patent No.  
9,496,699

## 0101108

### Recessed Light Converter Shelf Display

11.3" L x 9.3" W x 10.3" H

- Easily change ordinary recessed lights into beautiful, modern lighting.
- Display the Recessed Light Converter using our Shelf Merchandiser.
- The perfect way to display inventory and increase your sales.
- Each display comes with 6 pieces of the Recessed Light Converter.



Fixture assembly required.

## 09842

### DesignerYou® Shelf Display

26" L x 20" W x 16" H

- Provides merchandising flexibility - add the fixture that appeals to YOUR customers.
- Sturdy, stylish and easy to set up.
- Fits on almost any shelf (minimum 14" deep and 24" wide).
- Includes: display, header and plug-in electrical cord (fixture and glass sold separately).



## OUTDOOR LIGHT FIXTURES

Make a welcoming statement to visitors with the inviting glow of light. The timeless designs and durable craftsmanship of Westinghouse’s outdoor lighting fixtures provide lasting style and beauty.

# LED OUTDOOR LIGHT FIXTURE ASSORTMENT

INTEGRATED  
**LED**



**63120**  
Glenwillow  
**1 Light LED Wall Lantern**  
Victorian Bronze Finish  
with Clear Seeded Glass  
Height: 10.78" Width: 5.39" Extends: 6.97"  
Height from Center of Outlet Box: 3.50"  
Back Plate: H: 6.97" W: 4.33"  
Includes 8.5 Watt Integrated LED  
Incandescent version available on pg. 86

DIMMABLE  
**LED**



**New!**

**63234**  
Skyview  
**1 Light LED Wall Fixture**  
Oil Rubbed Bronze Finish  
with Mesh and Clear Glass  
Height: 13.35" Width: 7.01" Extends: 9.92"  
Height from Center of Outlet Box: 5"  
Back Plate: H: 10.04" W: 6.50"  
Includes (1) Medium (E26) Base,  
4.5 Watt T9 Filament LED Lamp  
Incandescent version available on pg. 86

INTEGRATED  
**LED**



**63183**  
Skyview  
**1 Light LED Wall Fixture**  
Brushed Nickel Finish with Mesh,  
Clear and Frosted Glass  
Height: 13.98" Width: 7.01" Extends: 9.92"  
Height from Center of Outlet Box: 5.51"  
Back Plate: H: 10.04" W: 6.50"  
Includes 12.5 Watt Integrated LED

INTEGRATED  
**LED**



**62034**  
Orson  
**1 Light LED Wall Lantern**  
Oil Rubbed Bronze Finish  
with Clear Prismatic Lens  
Height: 9.5" Width: 8.75" Extends: 10"  
Height from Center  
of Outlet Box: 4.21"  
Back Plate: D: 6.18"  
Includes 8 Watt Integrated LED

INTEGRATED  
**LED**



**62046**  
Orson  
**1 Light LED Wall Lantern**  
Oil Rubbed Bronze Finish  
with Clear Prismatic Lens  
Height: 11.61" Width: 10.63" Extends: 11.61"  
Height from Center  
of Outlet Box: 5.08"  
Back Plate: D: 6.18"  
Includes 9 Watt Integrated LED

INTEGRATED  
**LED**



**DARK SKY<sup>+</sup>**  
FRIENDLY

**+63155**  
Ithaca  
**1 Light LED Wall Fixture**  
Weathered Steel Finish  
with Metal Shade  
Height: 11.5" Width: 11.93" Extends: 15.35"  
Height from Center  
of Outlet Box: 4.13"  
Back Plate: D: 5"  
Includes 13.4 Watt Integrated LED

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
63120	*	8.5	60	2700 (Warm White)	260	80	20000	18.2	\$1.02
63234	*	4.5	60	2700 (Warm White)	450	80	15000	13.6	\$0.54
63183	*	12.5	60	2700 (Warm White)	410	80	20000	18.2	\$1.51
62034	*	8	40	2700 (Warm White)	500	80	20000	18.2	\$0.96
62046	*	9	40	2700 (Warm White)	550	80	20000	18.2	\$1.08
63155	*	13.4	75	3000 (Warm White)	900	80	30000	27.3	\$1.61

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).  
\* Integrated LED Light Source

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

<sup>†</sup>Dark Sky friendly fixtures aid in the reduction of light pollution.

# LED OUTDOOR LIGHT FIXTURE ASSORTMENT

INTEGRATED  
LED



**64001**  
1 Light LED Wall Lantern  
Black Finish with Seeded Glass  
Height: 11" Width: 6"  
Extends: 8"  
Height from Center of Outlet Box: 2.83"  
Back Plate: H: 5.38" W: 4.38"  
Includes 9 Watt Integrated LED

INTEGRATED  
LED



**62041**  
Darcy  
1 Light LED Wall Lantern  
Victorian Bronze Finish with Amber Frosted Glass  
Height: 11.89" Width: 7" Extends: 8"  
Height from Center of Outlet Box: 2.36"  
Back Plate: D: 4.53"  
Includes 8.5 Watt Integrated LED

INTEGRATED  
LED



**62047**  
Academy  
1 Light LED Wall Fixture  
Textured Black Finish with Chrome Cage  
Height: 11" Width: 12.13" Extends: 15.13"  
Height from Center of Outlet Box: 4.13"  
Back Plate: D: 5"  
Includes 13.4 Watt Integrated LED

**DARK SKY<sup>†</sup>**  
FRIENDLY



INTEGRATED  
LED

**63157**  
Mayslick  
2 Light LED  
Up and Down Light Wall Fixture  
Oil Rubbed Bronze Finish with Frosted Glass Lens  
Height: 12.20" Width: 5" Extends: 5.12"  
Height from Center of Outlet Box: 6.10"  
Back Plate: H: 5" W: 5"  
Includes 2 x 8.5 Watt Integrated LEDs

INTEGRATED  
LED



**63156**  
Mayslick  
1 Light LED Wall Fixture  
Oil Rubbed Bronze Finish with Frosted Glass Lens  
Height: 7.09" Width: 5" Extends: 5.12"  
Height from Center of Outlet Box: 3.54"  
Back Plate: H: 5" W: 5"  
Includes 8.5 Watt Integrated LED

**DARK SKY<sup>†</sup>**  
FRIENDLY

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
64001	*	9	40	3000 (Warm White)	500	80	40000	36.5	\$1.08
62041	*	8.5	40	2700 (Warm White)	450	80	20000	18.2	\$1.02
62047	*	13.4	60	3000 (Warm White)	900	80	30000	27.3	\$1.61
63157	*	17 (2 x 8.5)	120 (2 x 60)	2700 (Warm White)	909	80	20000	18.2	\$2.05
63156	*	8.5	60	2700 (Warm White)	428	80	20000	18.2	\$1.02
64000	*	9	40	3000 (Warm White)	500	80	40000	36.5	\$1.08
64002	*	9	40	3000 (Warm White)	500	80	40000	36.5	\$1.08
64003	*	9	40	3000 (Warm White)	500	80	35000	31.9	\$1.08
64004	*	9	40	3000 (Warm White)	500	80	35000	31.9	\$1.08

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).  
\* Integrated LED Light Source

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

<sup>†</sup>Dark Sky friendly fixtures aid in the reduction of light pollution.



# LED OUTDOOR LIGHT FIXTURE ASSORTMENT

INTEGRATED  
LED

**64000**  
**1 Light LED Wall Lantern**  
*Weathered Patina Finish with Seeded Glass*  
 Height: 12.25" Width: 6"  
 Extends: 8"  
 Height from Center of Outlet Box: 2.83"  
 Back Plate: H: 5.38" W: 4.38"  
 Includes 9 Watt Integrated LED



INTEGRATED  
LED

**64002**  
**1 Light LED Wall Lantern**  
*Oil Rubbed Bronze Finish with Frosted Glass*  
 Height: 14.63" Width: 6.25"  
 Extends: 8.75"  
 Height from Center of Outlet Box: 9.06"  
 Back Plate: H: 7.88" W: 4.50"  
 Includes 9 Watt Integrated LED



INTEGRATED  
LED

**64003**  
**1 Light LED Wall Lantern**  
*Oil Rubbed Bronze Finish with Crackle Glass*  
 Height: 9.75" Width: 6"  
 Extends: 7.88"  
 Height from Center of Outlet Box: 2.83"  
 Back Plate: H: 5.38" W: 4.38"  
 Includes 9 Watt Integrated LED



INTEGRATED  
LED

**64004**  
**1 Light LED Wall Lantern**  
*Oil Rubbed Bronze Finish with Crackle Glass*  
 Height: 11.75" Width: 9"  
 Extends: 11.75"  
 Height from Center of Outlet Box: 2.83"  
 Back Plate: H: 8.88" W: 6.50"  
 Includes 9 Watt Integrated LED



## LED FIXTURE SHELF DISPLAY

- Provides merchandising flexibility - add the fixture that appeals to YOUR customers.
- Sturdy, stylish and easy to set up.
- Fits on almost any shelf (minimum 14" deep and 24" wide).
- Includes: display, header and plug-in electrical cord (fixture sold separately).

**09844**  
**LED Outdoor Fixture Shelf Display**  
 26" L x 20" W x 16" H



Fixture assembly required.

# OUTDOOR LIGHT FIXTURE ASSORTMENT

**63123**  
**Valley Forge**  
**1 Light Wall Lantern**  
 Matte Black Finish  
 with Copper Accents  
 and Frosted Chimney  
 in Clear Seeded Glass  
 Height: 17" Width: 9.25" Extends: 12.75"  
 Height from Center of Outlet Box: 10.75"  
 Back Plate: H: 8" W: 4.96"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



Washed Copper  
 Detail Shown



**63215**  
**Valley Forge**  
**2 Light Wall Lantern**  
 Oil Rubbed Bronze Finish  
 with Clear Seeded Glass  
 Height: 17" Width: 9.25"  
 Extends: 12.75"  
 Height from Center  
 of Outlet Box: 10.75"  
 Back Plate: H: 8" W: 4.96"  
 Use (2) Candelabra (E12)  
 Base Lamps, 40 Watt Maximum



**63126**  
**Albright**  
**1 Light Pendant**  
 Textured Black Finish  
 with Amber Frosted and  
 Clear Seeded Glass  
 Height: 13.19" Diameter: 8.19"  
 Chain: 36" Cord: 60"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



Frosted Amber  
 and Clear Seeded  
 Glass Detail Shown




**63124**  
**Albright**  
**1 Light Medium Wall Lantern**  
 Textured Black Finish with  
 Amber Frosted and Clear Seeded Glass  
 Height: 14.09" Width: 7.01" Extends: 8.78"  
 Height from Center of Outlet Box: 4.25"  
 Back Plate: H: 8.46" W: 5.51"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**63125**  
**Albright**  
**1 Light Large Wall Lantern**  
 Textured Black Finish with  
 Amber Frosted and Clear Seeded Glass  
 Height: 15.04" Width: 8.19" Extends: 9.41"  
 Height from Center of Outlet Box: 4.25"  
 Back Plate: H: 8.46" W: 5.51"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**63182**  
**Skyview**  
**1 Light Pendant**  
 Oil Rubbed Bronze Finish  
 with Mesh and Clear Glass  
 Height: 13.38" Diameter: 7.01"  
 Chain: 36" Cord: 60"  
 Includes (1) Medium (E26) Base,  
 T9 Vintage Lamp, 60 Watt



Mesh Detail Shown

also  
 available in  
**LED**



**63181**  
**Skyview**  
**1 Light Wall Fixture**  
 Oil Rubbed Bronze Finish  
 with Mesh and Clear Glass  
 Height: 13.35" Width: 7.01" Extends: 9.92"  
 Height from Center of Outlet Box: 5"  
 Back Plate: H: 10.04" W: 6.50"  
 Includes (1) Medium (E26) Base,  
 T9 Vintage Lamp, 60 Watt  
**Replacement Lamp WLC #04118**

also  
 available in  
**LED**



**63150**  
**Glenwillow**  
**1 Light Wall Lantern**  
 Victorian Bronze Finish  
 with Amber Frosted Glass  
 Height: 10.78" Width: 5.39" Extends: 6.97"  
 Height from Center of Outlet Box: 3.50"  
 Back Plate: H: 6.97" W: 4.33"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum

Add Westinghouse  
 Filament LED or Timeless lamps  
 for the vintage look you want.

 **Westinghouse**  
**VINTAGE LAMPS**



COORDINATE WITH THE CALISTE & CLARISSA COLLECTIONS



**62048**  
Orwell  
**2 Light Flush**  
Textured Black Finish with Frosted Seeded Glass  
Height: 4.60" Square: 11"  
Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



**62039**  
Clarissa  
**1 Light Wall Fixture**  
Oil Rubbed Bronze Finish with Highlights and Clear Seeded Glass  
Height: 6.30" Width: 4.57"  
Extends: 8.78"  
Height from Center of Outlet Box: 3.15"  
Back Plate: H: 6.30" W: 4.57"  
Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**62038**  
Clarissa  
**1 Light Wall Fixture**  
Textured Black Finish with Frosted Glass  
Height: 11.22" Width: 7"  
Extends: 8.78"  
Height from Center of Outlet Box: 3.15"  
Back Plate: H: 6.30" W: 4.57"  
Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**62045**  
Caliste  
**1 Light Wall Fixture with Dusk to Dawn Sensor**  
Textured Black Finish with Clear Water Glass  
Height: 10" Width: 6"  
Extends: 7.75"  
Height from Center of Outlet Box: 4"  
Back Plate: H: 8" W: 5"  
Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63148**  
Foxport  
**1 Light Wall Fixture**  
Textured Black Finish with Frosted White Opal Glass  
Height: 13.54" Width: 8.50"  
Extends: 11.80"  
Height from Center of Outlet Box: 9.69"  
Back Plate: D: 6.38"  
Use (1) Medium (E26) Base Lamp, 60 Watt Maximum

**DARK SKY<sup>+</sup>**  
FRIENDLY

**†62043**  
Roosevelt  
**1 Light Wall Lantern**  
Amber Bronze Finish with Highlights  
Height: 9.48" Width: 7.48"  
Extends: 8.66"  
Height from Center of Outlet Box: 3.11"  
Back Plate: D: 4.88"  
Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**DARK SKY<sup>+</sup>**  
FRIENDLY

**†62044**  
Watts Creek  
**1 Light Wall Lantern**  
Textured Black Finish  
Height: 11.02" Width: 11"  
Extends: 12.60"  
Height from Center of Outlet Box: 6.14"  
Back Plate: D: 5.71"  
Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



<sup>†</sup>Dark Sky friendly fixtures aid in the reduction of light pollution.



# OUTDOOR LIGHT FIXTURE ASSORTMENT



**63131**  
**Delmont**  
**1 Light Wall Fixture**  
*Oil Rubbed Bronze Finish with Highlights and Clear Water Glass*  
 Height: 13.35" Width: 10" Extends: 12.24"  
 Height from Center of Outlet Box: 5.83"  
 Back Plate: D: 6.38"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63134**  
**Delmont**  
**1 Light Wall Fixture**  
*Oil Rubbed Bronze Finish with Highlights and Clear Textured Glass*  
 Height: 13.80" Width: 10" Extends: 12.24"  
 Height from Center of Outlet Box: 5.83"  
 Back Plate: D: 6.38"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**63135**  
**Delmont**  
**1 Light Wall Fixture**  
*Oil Rubbed Bronze Finish with Highlights and Clear Seeded Glass*  
 Height: 14.32" Width: 10" Extends: 12.24"  
 Height from Center of Outlet Box: 5.83"  
 Back Plate: D: 6.38"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**62040**  
**Emma Jane**  
**1 Light Wall Lantern**  
*Amber Bronze Finish with Highlights and Clear Seeded Glass*  
 Height: 10" Width: 6.69"  
 Extends: 8.85"  
 Height from Center of Outlet Box: 5.43"  
 Back Plate: D: 6.38"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum

**62042**  
**Santa Fe**  
**1 Light Wall Lantern**  
*Weathered Bronze Finish with Frosted Glass*  
 Height: 11.22" Width: 7.67"  
 Extends: 9.84"  
 Height from Center of Outlet Box: 4.72"  
 Back Plate: H: 5.98" W: 4.49"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**62301**  
**Weatherby**  
**1 Light Wall Lantern**  
*Weathered Bronze Finish with Clear Glass*  
 Height: 12.75" Width: 6" Extends: 7.50"  
 Height from Center of Outlet Box: 7.25"  
 Back Plate: H: 7.88" W: 4.38"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**64841**  
**Studenburg**  
**1 Light Wall Lantern**  
*Vintage Bronze Finish with Clear Crackle Glass*  
 Height: 12.88" Width: 7" Extends: 8.87"  
 Height from Center of Outlet Box: 7.25"  
 Back Plate: H: 6.50" W: 4.13"  
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



**62306**  
**New Haven**  
**1 Light Wall Lantern**  
*Oil Rubbed Bronze Finish with Clear Seeded Glass*  
 Height: 13.75" Width: 6.50" Extends: 8.63"  
 Height from Center of Outlet Box: 4.88"  
 Back Plate: D: 4.75"  
 Back Plate: H: 6.88" W: 4.50"  
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum

Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.







**63137**  
Eddystone  
**1 Light Wall Fixture**  
with Dusk to Dawn Sensor  
Oil Rubbed Bronze Finish  
with Clear Diamond Cut Glass  
Height: 9.53" Width: 6.63"  
Extends: 8.66"  
Height from Center  
of Outlet Box: 4.65"  
Back Plate: D: 5"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum



**63142**  
Eddystone  
**1 Light Wall Fixture**  
Brushed Nickel Finish  
with Clear Ribbed Glass  
Height: 9.69" Width: 5.91"  
Extends: 8.54"  
Height from Center  
of Outlet Box: 4.65"  
Back Plate: D: 5"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum



**63143**  
Eddystone  
**1 Light Wall Fixture**  
Textured Black Finish  
with White Opal Glass  
Height: 8.19" Width: 6"  
Extends: 8.86"  
Height from Center  
of Outlet Box: 4.65"  
Back Plate: D: 5"  
Use (1) Medium (E26) Base Lamp,  
60 Watt Maximum

**62307**  
Parksville  
**1 Light Wall Lantern**  
Oil Rubbed Bronze Finish  
with White Alabaster Glass  
Height: 11" Width: 6.25" Extends: 8.37"  
Height from Center of Outlet Box: 2.25"  
Back Plate: D: 4.75"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**62303**  
Bonneville  
**2 Light Flush**  
Weathered Bronze Finish  
with Frosted Glass  
Height: 5.63" Diameter: 12.63"  
Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum



**66741**  
Senecaville  
**1 Light Wall Lantern**  
Weathered Bronze Finish  
with White Alabaster Glass  
Height: 13.13" Width: 6.50" Extends: 8"  
Height from Center of Outlet Box: 5.25"  
Back Plate: H: 6.13" W: 5.25"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**66742**  
Senecaville  
**1 Light Wall Lantern**  
Weathered Bronze Finish  
with White Alabaster Glass  
Height: 16.25" Width: 8" Extends: 9.50"  
Height from Center of Outlet Box: 6.50"  
Back Plate: H: 7.50" W: 6.50"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**66746**  
Senecaville  
**2 Light Flush**  
Weathered Bronze Finish  
with White Alabaster Glass  
Height: 6" Diameter: 12"  
Use (2) Medium (E26)  
Base Lamps, 60 Watt Maximum



# OUTDOOR LIGHT FIXTURE ASSORTMENT



**62309**

**Naveen**

**2 Light Flush**

*Oil Rubbed Bronze Finish  
with White Alabaster Glass*

*Height: 6" Diameter: 13"*

*Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum*



**69407**

**Claremont**

**2 Light Flush**

*Textured Rust Patina Finish  
with White Alabaster Glass*

*Height: 5" Diameter: 12"*

*Use (2) Medium (E26) Base Lamps,  
60 Watt Maximum*



**67831**

**1 Light Wall Lantern**

*Textured Black Finish  
with Clear Beveled Glass*

*Height: 12.01" Width: 6.57" Extends: 7.80"*

*Height from Center of Outlet Box: 2.83"*

*Back Plate: H: 5.75" W: 4.38"*

*Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum*



**67834**

**1 Light Wall Lantern**

*Textured White Finish  
with Clear Beveled Glass*

*Height: 12.01" Width: 6.57" Extends: 7.80"*

*Height from Center of Outlet Box: 2.83"*

*Back Plate: H: 5.75" W: 4.38"*

*Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum*

**66964**  
**1 Light Wall Lantern**

*Polished Brass Finish  
with Clear Glass*  
Height: 13.50"  
Width: 4.75"  
Extends: 5.75"  
Height from Center  
of Outlet Box: 8"  
Back Plate: D: 4.50"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**66983**  
**1 Light Wall Lantern**

*Matte Black Finish  
with Clear Glass*  
Height: 13.50"  
Width: 4.75"  
Extends: 5.75"  
Height from Center  
of Outlet Box: 8"  
Back Plate: D: 4.50"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**66961**  
**1 Light Wall Lantern**

*Matte Black Finish  
with Clear Curved Glass*  
Height: 7.75" Width: 6" Extends: 6.50"  
Height from Center of Outlet Box: 2.25"  
Back Plate: D: 4.50"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**64688**  
**1 Light Wall Lantern**

*Antique Silver Finish  
with Clear Curved Glass*  
Height: 7.75" Width: 6" Extends: 6.50"  
Height from Center of Outlet Box: 2.25"  
Back Plate: D: 4.50"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**64689**  
**1 Light Wall Lantern**

*Textured Rust Patina Finish  
with Clear Curved Glass*  
Height: 7.75" Width: 6" Extends: 6.50"  
Height from Center of Outlet Box: 2.25"  
Back Plate: D: 4.50"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**66924**  
**1 Light Wall Lantern**

*Polished Brass Finish  
with Clear Curved  
Beveled Glass*  
Height: 18.50" Width: 5.75"  
Extends: 6"  
Height from Center  
of Outlet Box: 11.50"  
Back Plate: D: 4.50"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**66970**  
**1 Light Wall Lantern**

*Polished Brass Finish  
with Clear Curved  
Beveled Glass*  
Height: 15" Width: 6.50"  
Extends: 7"  
Height from Center  
of Outlet Box: 7.50"  
Back Plate: H: 5.50" W: 4.75"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



**66853**  
**1 Light Wall Lantern**

*Polished Brass Finish  
with Clear Beveled Glass*  
Height: 12" Width: 7" Extends: 7"  
Height from Center of Outlet Box: 2.75"  
Back Plate: H: 5.50" W: 4.75"  
Use (1) Medium (E26) Base Lamp,  
100 Watt Maximum



# OUTDOOR LIGHT FIXTURE ASSORTMENT



**64829**  
 Nova Scotia  
**1 Light Wall Lantern**  
 with Dusk to Dawn Sensor  
 Textured Black Finish  
 with Honey Art Glass  
 Height: 11" Width: 6.25" Extends: 8.87"  
 Height from Center of Outlet Box: 4.50"  
 Back Plate: H: 8.43" W: 4.13"  
 Includes (1) GU24 Base, 13 Watt CFL Twist



**67328**  
 Burnham  
**1 Light Wall Lantern**  
 Oil Rubbed Bronze Finish  
 with Honey Art Glass  
 Height: 12.5" Width: 6" Extends: 9"  
 Height from Center of Outlet Box: 2.50"  
 Back Plate: H: 5" W: 5"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**66898**  
**1 Light Wall Lantern**  
 Textured Black Finish  
 with White Acrylic Lens  
 Height: 9.75" Width: 7.75" Extends: 4.13"  
 Height from Center of Outlet Box: 4.25"  
 Back Plate: H: 9.38" W: 7"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**64883**  
**1 Light Wall Lantern**  
 with Dusk to Dawn Sensor  
 Sienna Finish with Frosted Glass  
 Height: 8.25" Width: 4.50" Extends: 5.75"  
 Height from Center of Outlet Box: 3"  
 Back Plate: D: 4.50"  
 Includes (1) GU24 Base, 13 Watt CFL Twist



**69919**  
**1 Light Wall Lantern**  
 Brushed Nickel Finish  
 with Clear Textured Glass  
 Height: 12" Width: 6.25" Extends: 7.25"  
 Height from Center of Outlet Box: 7"  
 Back Plate: H: 6.10" W: 4.33"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**67930**  
**1 Light Wall Lantern**  
 Bronze Patina Finish  
 with Clear Textured Glass  
 Height: 12" Width: 6.25" Extends: 7.25"  
 Height from Center of Outlet Box: 7"  
 Back Plate: H: 6.10" W: 4.33"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**66972**  
**1 Light Wall Lantern**  
 Textured Black Finish with Clear Glass  
 Height: 8.25" Width: 4.50" Extends: 5.75"  
 Height from Center of Outlet Box: 3"  
 Back Plate: D: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**64684**  
**1 Light Wall Lantern**  
 Antique Silver Finish with Clear Glass  
 Height: 8.25" Width: 4.50" Extends: 5.75"  
 Height from Center of Outlet Box: 3"  
 Back Plate: D: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**66971**  
**1 Light Wall Lantern**  
 White Finish with Clear Glass  
 Height: 8.25" Width: 4.50" Extends: 5.75"  
 Height from Center of Outlet Box: 3"  
 Back Plate: D: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum

Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).





**66919**  
**1 Light Flush**  
 Matte Black Finish  
 with Clear Glass  
 Height: 6" Diameter: 4.75"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**66818**  
**1 Light Flush**  
 Antique Brass Finish  
 with Clear Glass  
 Height: 6" Diameter: 4.75"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**66885**  
**1 Light Wall Fixture**  
 Matte Black Finish  
 with Clear Glass  
 Height: 7.50" Diameter: 4.50"  
 Extends: 5.75"  
 Height from Center of Outlet Box: 2"  
 Back Plate: D: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**66884**  
**1 Light Wall Fixture**  
 Polished Brass Finish  
 with Clear Glass  
 Height: 7.50" Diameter: 4.50"  
 Extends: 5.75"  
 Height from Center of Outlet Box: 2"  
 Back Plate: D: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**66878**  
**1 Light Wall Fixture**  
 White Finish  
 with Clear Glass  
 Height: 7.50" Diameter: 4.50"  
 Extends: 5.75"  
 Height from Center of Outlet Box: 2"  
 Back Plate: D: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**66882**  
**1 Light Wall Fixture**  
 Oil Rubbed Bronze Finish  
 with Clear Ribbed Glass  
 Height: 7.50" Diameter: 4.50" Extends: 5.75"  
 Height from Center of Outlet Box: 2"  
 Back Plate: D: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 100 Watt Maximum



**66800**  
**1 Light**  
**Hi-Impact Polypropylene**  
**Wall Fixture**  
 Black Finish with Clear Glass  
 Height: 6" Diameter: 4.50" Extends: 5.75"  
 Height from Center of Outlet Box: 2.50"  
 Back Plate: H: 4.38" W: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**66949**  
**1 Light Hi-Impact Polycarbonate**  
**Wall Fixture with**  
**Dusk to Dawn Sensor**  
 Black Finish with Clear Glass  
 Height: 6" Diameter: 4.50" Extends: 5.75"  
 Height from Center of Outlet Box: 2.50"  
 Back Plate: H: 4.38" W: 4.50"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



# OUTDOOR LIGHT FIXTURE ASSORTMENT

**67835**  
**1 Light Wall Fixture**  
 White Finish  
 with White Glass Lens  
 Height: 4.92" Width: 8.27"  
 Extends: 4.13"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum



**67836**  
**1 Light Wall Fixture**  
 White Finish  
 with White Glass Lens  
 Diameter: 7.76"  
 Extends: 4.06"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum



**66881**  
**1 Light Wall Lantern**  
 Textured Black Finish  
 with Frosted Glass  
 Height: 8.50" Width: 6"  
 Extends: 6.75"  
 Height from Center  
 of Outlet Box: 3.88"  
 Back Plate: D: 4.75"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum



**66879**  
**1 Light Wall Lantern**  
 Textured White Finish  
 with Frosted Glass  
 Height: 8.50" Width: 6"  
 Extends: 6.75"  
 Height from Center  
 of Outlet Box: 3.88"  
 Back Plate: D: 4.75"  
 Use (1) Medium (E26)  
 Base Lamp, 60 Watt Maximum




**DARK SKY<sup>†</sup>**  
 FRIENDLY


**†67973**  
**1 Light Wall Fixture**  
 Polished Graphite Finish  
 Height: 7" Width: 4.50"  
 Extends: 7.87"  
 Height from Center  
 of Outlet Box: 2.76"  
 Back Plate: H: 5" W: 4.25"  
 Use (1) Medium (E26)  
 Base Lamp, 75 Watt Maximum



**67975**  
**2 Light Up and Down  
 Light Wall Fixture**  
 Polished Graphite Finish  
 Height: 15" Width: 5"  
 Extends: 8.25"  
 Height from Center  
 of Outlet Box: 7.5"  
 Back Plate: H: 5" W: 4.25"  
 Use (2) Medium (E26)  
 Base Lamps, 75 Watt Maximum



**66808**  
**Lantern Post**  
 Black Finish  
 Height: 84" Width: 3"  
 (Includes ladder rest)




**66955**  
**Lantern Post  
 with Ground  
 Convenience Outlet  
 & Dusk to Dawn  
 Sensor**  
 Black Finish  
 Height: 84" Width: 3"  
 (Includes ladder rest)



**66991**  
**Steel Ladder Rest and  
 Polycarbonate Spherettes**  
 Black Finish  
 Diameter: 1.38" Width: 15.75"



**67901**  
**Pedestal Mount  
 for Post Lantern**  
 Textured Black Finish  
 Height: 3.11"  
 Square: 5.67"



Designed for use with post top lanterns that fit a 3" diameter post. (Not intended to be used with a lantern post.)

<sup>†</sup>Dark Sky friendly fixtures aid in the reduction of light pollution.



**66803**  
**1 Light Hi-Impact Polycarbonate Wall Fixture**  
*Black Finish with White Glass Globe*  
 Height: 7.25" Diameter: 6" Extends: 7"  
 Height from Center of Outlet Box: 2.50"  
 Back Plate: H: 4.38" W: 4.50"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**67978**  
**1 Light Wall Fixture**  
*Brushed Aluminum Finish with White Threaded Glass Globe*  
 Height: 7" Diameter: 5.75" Extends: 7"  
 Height from Center of Outlet Box: 3.25"  
 Back Plate: H: 5.88" W: 4.50"  
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



**66840**  
**1 Light Flush**  
*Black Finish with White Glass Globe*  
 Height: 7.25" Diameter: 6"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



**66861**  
**1 Light Polycarbonate Post Top Lantern**  
*Black Finish with White Acrylic Globe*  
 Height: 13" Diameter: 12"  
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum  
 (Fits standard 3" post, post sold separately)

## LIGHT FIXTURE SHELF DISPLAY

- Provides merchandising flexibility - add the fixture that appeals to YOUR customers.
- Sturdy, stylish and easy to set up.
- Fits on almost any shelf (minimum 14" deep and 24" wide).
- Includes: display, header and plug-in electrical cord (fixture sold separately).



**09843**  
**Light Fixture Shelf Display**  
 26" L x 20" W x 16" H

Fixture assembly required.

# OUTDOOR LIGHT FIXTURE ASSORTMENT



**66823**  
**2 Light Hi-Impact Polypropylene Flush**  
 Black Finish with Clear Textured Glass  
 Height: 5.50" Square: 10.25"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**66976**  
**2 Light Hi-Impact Polypropylene Flush**  
 White Finish with Clear Textured Glass  
 Height: 5.50" Square: 10.25"  
 Use (2) Medium (E26) Base Lamps,  
 60 Watt Maximum



**66822**  
**1 Light Hi-Impact Polypropylene Flush**  
 Black Finish with Clear Textured Glass  
 Height: 4.75" Square: 8.25"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**66975**  
**1 Light Hi-Impact Polypropylene Flush**  
 White Finish with Clear Textured Glass  
 Height: 4.75" Square: 8.25"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**66859**  
**1 Light Hi-Impact Polypropylene Wall Lantern**  
 Black Finish with Clear Textured Acrylic  
 Height: 8" Width: 7.25" Extends: 6"  
 Height from Center of Outlet Box: 2.37"  
 Back Plate: D: 4.75"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum



**66946**  
**1 Light Hi-Impact Polycarbonate Wall Lantern with Removable Tail**  
 White Finish with Clear Textured Acrylic  
 Height with Tail: 17"  
 Height without Tail: 13"  
 Square: 8" Extends: 8.50"  
 Height from Center of Outlet Box: 10.75"  
 Back Plate: H: 4.63" W: 4.63"  
 Use (1) Medium (E26) Base Lamp,  
 60 Watt Maximum




**66875**  
**1 Light Hi-Impact Polycarbonate Post Top Lantern**  
 Black Finish with Clear Textured Acrylic  
 Height: 12.38" Square: 8"  
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum  
 (Fits standard 3" post, post sold separately)





# Westinghouse


INNOVATION YOU CAN BE SURE OF



**75052**  
7" Picture Light  
*Antique Brass Finish*  
Extends 5 7/8" From Wall  
Includes (1) T6,  
15 Watt Frost Lamp



**75050**  
7" Picture Light  
*Polished Brass Finish*  
Extends 5 7/8" From Wall  
Includes (1) T6,  
15 Watt Frost Lamp



**75051**  
14" Picture Light  
*Polished Brass Finish*  
Extends 6" From Wall  
Includes (2) T6,  
15 Watt Frost Lamps



**75053**  
14" Picture Light  
*Antique Brass Finish*  
Extends 6" From Wall  
Includes (2) T6,  
15 Watt Frost Lamps

**Picture Light Replacement Lamp**  
**#03723 T6 15 Watt**  
**Candelabra Base**

## ACCENT LIGHTING PICTURE LIGHTS

Picture lights amplify the natural beauty of treasured artwork and photographs.

Includes:

- Adjustable Neck and Shade.
- 8' Cord Set.
- In-line On/Off Switch.
- Detachable Polarized Plug.
- Mounting Hardware.
- Westinghouse T6, 15 Watt, Candelabra Base Lamp.

# CEILING FANS



## Low Ceilings




Westinghouse offers a wide array of attractive hugger and combo mount ceiling fans that are ideal for rooms with low ceilings.



## Standard 8 Ft. Ceilings

In rooms with standard 8 ft. ceilings, choose to mount your ceiling fan with or without a down rod.

### What Size Ceiling Fan Do You Need?



In order to ensure completely energy-efficient operation, make sure the size of the ceiling fan is appropriate for the size and height of your room. If the ceiling fan is too small for the room, it has to run at a higher speed in order to be effective, which wastes energy.

All ceiling fans in this catalog are UL or ETL Listed.





# THE BEST CEILING FAN FOR EVERY ROOM



## High Ceilings


Maximize the use of your ceiling fan in rooms with high ceilings by installing an extension down rod.



## Angled Ceilings

In rooms with angled or sloped ceilings, an extension down rod should be installed with the fan to optimize performance. For remote control installation, a cathedral ceiling fan canopy kit is recommended. *(Shown on page 148.)*

### What Size Down Rod Do You Need?



\*For 8 ft. ceilings, hugger (low profile) ceiling fans can be used.

# OPTIMIZE YOUR CEILING FAN'S EFFICIENCY



## DC Motor Fans

### A Smart Choice

DC motors offer significant energy savings, consuming up to 57% less energy compared to AC ceiling fans. This means reduced operating costs and a minimized environmental impact. These highly-efficient ceiling fans also boast more speed options, faster acceleration, extremely balanced construction, and incredibly quiet operation.



## LED Light Options

### Integrated LED or LED Lamps

On average, LEDs consume 80% less energy when compared to incandescent lamps and are mercury-free, which means considerably reduced energy costs and a minimized carbon footprint. Plus, they last much longer than any alternative, so changing lamps in hard-to-reach ceiling fans will become a rare occurrence.



Look for these symbols to indicate important energy-saving features for ceiling fans.






## ENERGY GUIDE LABELS

New FTC Energy Guide Labels will be included on ALL ceiling fans. These labels must be printed on packaging by January 1, 2018. Westinghouse has proactively begun updating the packaging with these labels.

The new FTC yellow Energy Guide Labels represent averages for airflow, wattage and energy costs.

### NEW FTC ENERGY GUIDE LABELS



Westinghouse will continue to show the Airflow Performance Label with the actual performance specifications at different speeds on applicable fans.

### AIRFLOW PERFORMANCE LABEL

Performance and Energy Information			
Fan Speed	Airflow (CFM)	Power Use (Watts)	Airflow Efficiency (CFM/Watt)
Low	1,184	11	108
Medium	2,591	26	100
High	3,914	56	70

## Performance / Energy

### Understand Your Ceiling Fan's Performance Characteristics

- **Airflow** is measured in **CFMs** (Cubic Feet per Minute or volume of air the ceiling fan can move).
- **Watts Used** is the amount of electricity used by the ceiling fan.
- **Efficiency** is measured in **CFM/Watts** (amount of air a ceiling fan moves in CFM divided by the amount of electricity it uses in Watts).

As of January 2017, all Westinghouse hugger ceiling fans include lamps.



## Summer / Winter Mode

Most of our ceiling fans include a reversible switch allowing you to keep your room cool in the summer or re-circulate warm air from the ceiling in the winter.

### A Pleasant, Gentle Breeze

In the summer, Westinghouse ceiling fans keep your home pleasantly cool. The ceiling fan runs counterclockwise, and sets the air in motion. The airflow creates a wind chill effect on your skin. Summer mode allows you to lower energy costs while keeping you cool.

### Increase Comfort Level

In the winter, Westinghouse ceiling fans can be switched to the clockwise direction. As a result, the warm air that collects near the ceiling is distributed evenly throughout the room and eliminates cold spots and drafts. It dramatically increases your comfort level and decreases heating costs.

See page 144 for ceiling fans that have a reverse airflow function.



**Westinghouse**

INNOVATION YOU CAN BE SURE OF



## CONTEMPORARY CEILING FANS

Featuring a wide range of modern and transitional styles, our contemporary collection of ceiling fans captures the essence of today's lifestyle trends with striking, stylish designs and sleek finishes.

# Techno II

Cool large areas and lofts in style with a highly-efficient DC motor and LED light kit.

**72042**

**72" Black Finish**

Black ABS Blades

Includes Light Kit with Opal Frosted Glass



**New!**



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Remote Control
- 6 Fan Speeds
- Includes 17.5 Watt Integrated LED

**Airflow:** 7234 Cubic Feet Per Minute

**Electricity Use:** 31 Watts (excludes lights)

**Airflow Efficiency:** 233 Cubic Feet Per Minute Per Watt

**72039**

**72" Titanium Finish**

Titanium ABS Blades

Includes Light Kit with Opal Frosted Glass



**New!**



# Techno

Curved blades surround an efficient LED light kit on this sophisticated design.

**78002**

**52" Brushed Aluminum Finish**

Gray ABS Blades

Includes Light Kit with Opal Frosted Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Remote Control
- 4 Fan Speeds
- Includes 17.5 Watt Integrated LED

**Airflow:** 4187 Cubic Feet Per Minute

**Electricity Use:** 53 Watts (excludes lights)

**Airflow Efficiency:** 79 Cubic Feet Per Minute Per Watt

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72042	*	17.5	100	3000 (Warm White)	1250	80	25000	22.8	\$2.11
72039	*	17.5	100	3000 (Warm White)	1250	80	25000	22.8	\$2.11
78002	*	17.5	75	3000 (Warm White)	925	80	25000	22.8	\$2.05

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\* Integrated LED Light Source

\*\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh



# Cayuga

*This ceiling fan is a masterpiece that looks outstanding as it cools any larger space, from great rooms to large bedrooms.*

**72077**

**60" Brushed Nickel Finish**

*Reversible Blades (Rosewood/Light Maple)  
Includes Light Kit with Opal Frosted Glass*

**New!**



DIMMABLE  
**LED**



## SPECIFICATIONS

- 3/4" X 6" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 6098 Cubic Feet Per Minute

**Electricity Use:** 81 Watts (excludes lights)

**Airflow Efficiency:** 75 Cubic Feet Per Minute Per Watt

**72078**

**60" Oil Rubbed Bronze Finish**

*Reversible Blades (Applewood/Cherry)  
Includes Light Kit with Opal Frosted Glass*

**New!**



DIMMABLE  
**LED**





# Zephyr

Refined details are distinctively modern and sophisticated.

72046

**56" Brushed Nickel Finish**

Reversible Blades (Rich Walnut/Maple)  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- 3/4" X 6" Down Rod
- Includes Remote Control
- 4 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 5450 Cubic Feet Per Minute

**Electricity Use:** 69 Watts (excludes lights)

**Airflow Efficiency:** 79 Cubic Feet Per Minute Per Watt



# Bolton

Bold, squared-off blades and tonal finishes make a stunning statement in larger rooms.

72040

**52" Brushed Aluminum Finish**

Reversible Blades (Graphite/Silver)  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Remote Control
- 4 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 4625 Cubic Feet Per Minute

**Electricity Use:** 60 Watts (excludes lights)

**Airflow Efficiency:** 77 Cubic Feet Per Minute Per Watt



# Desoto

Unique, free-floating blade brackets and beautiful finishes combine for a distinguished design.

72074

**52" Oil Rubbed Bronze Finish**

Reversible Blades (Mahogany/Cherry)  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- 3/4" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 4861 Cubic Feet Per Minute

**Electricity Use:** 60 Watts (excludes lights)

**Airflow Efficiency:** 81 Cubic Feet Per Minute Per Watt



## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72077	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	25000	22.8	\$1.92
72078	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	25000	22.8	\$1.92
72046	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	25000	22.8	\$1.92
72040	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	25000	22.8	\$1.92
72074	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$1.92

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Alta Vista

A stylish, energy-efficient choice for larger living areas and bedrooms.

**72059**

**52" Matte Black Finish**

Reversible Blades (Black/Bleached Cherry)  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Remote Control
- 4 Fan Speeds
- Includes 18 Watt Integrated LED

**Airflow:** 4789 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 81 Cubic Feet Per Minute Per Watt



# Castle LED

Beautiful craftsmanship coupled with a long-lasting LED light kit equals quality and performance.

**72091**

**52" Brushed Nickel Finish**

Reversible Blades (Weathered Maple/Beech)  
Includes Light Kit with Opal Frosted Glass


## SPECIFICATIONS

- ¾" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 3914 Cubic Feet Per Minute

**Electricity Use:** 56 Watts (excludes lights)

**Airflow Efficiency:** 70 Cubic Feet Per Minute Per Watt



## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72059	*	18	75	3000 (Warm White)	1080	80	25000	22.8	\$2.17
72091	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$1.92

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

\*Integrated LED Light Source

# Castle

Impressive light kit featuring lustrous brushed nickel bands provides both ample illumination and style.

**72477**

**52" Brushed Nickel Finish**

Reversible Blades (Weathered Maple/Beech)  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS


- ¾" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 13 Watt CFL Mini-Twists

**Airflow:** 3914 Cubic Feet Per Minute

**Electricity Use:** 56 Watts (excludes lights)

**Airflow Efficiency:** 70 Cubic Feet Per Minute Per Watt



Compact Fluorescent Lamps contain mercury.  For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

# Zander

Smooth curves and refined details bring a modern touch to any space.

**72011**

**52" Gun Metal Finish**

Reversible Blades (Applewood/Black)  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ½" X 6" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 13 Watt CFL Mini-Twists

**Airflow:** 4580 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 78 Cubic Feet Per Minute Per Watt



Compact Fluorescent Lamps contain mercury. (Hg) For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

# Comet

Sleek, casual and available in various finishes, this design is ideal for any contemporary or transitional space.

**7813665**

**52" Brushed Pewter Finish**

Reversible Blades (Light Maple/White)  
Includes Light Kit with Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 40 Watt Torpedo Lamps

**Airflow:** 3589 Cubic Feet Per Minute

**Electricity Use:** 63 Watts (excludes lights)

**Airflow Efficiency:** 57 Cubic Feet Per Minute Per Watt



**7801665**

**52" Matte Black Finish**

Reversible Blades (Matte Black/Marble)  
Includes Light Kit with Frosted Glass



**7801765**

**52" White Finish**

Reversible Blades  
(White/White Washed Pine)  
Includes Light Kit with Frosted Glass



# Alloy II

Clean, contemporary ceiling fan adds casual elegance.

**72051**

**52" Brushed Nickel Finish**

Reversible Blades (Rosewood/Light Maple)  
Includes Light Kit with Opal Frosted Glass

**New!**



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 4584 Cubic Feet Per Minute  
**Electricity Use:** 60 Watts (excludes lights)  
**Airflow Efficiency:** 76 Cubic Feet Per Minute Per Watt



# Alloy LED

An eye-catching ceiling fan with sleek, modern style.

**72053**

**52" Gun Metal Finish**

Reversible Blades (Black/Applewood)  
Includes Light Kit with Opal Frosted Glass

**New!**



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 3576 Cubic Feet Per Minute  
**Electricity Use:** 61 Watts (excludes lights)  
**Airflow Efficiency:** 59 Cubic Feet Per Minute Per Watt



**72090**

**52" Brushed Nickel Finish**

Reversible Blades (Beech/Wengue)  
Includes Light Kit with Opal Frosted Glass

**New!**



## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
<b>72051</b>	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$1.92
<b>72053</b>	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$1.92
<b>72090</b>	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$1.92

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh



# Alloy

Powerful air circulation combined with appealing details, this design is available in popular sizes and finishes.

**72041**

**52" Brushed Nickel Finish**

Reversible Blades (Beech/Wengue)

Includes Light Kit with Opal Frosted Glass



## SPECIFICATIONS


- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 13 Watt CFL Mini-Twists

**Airflow:** 3476 Cubic Feet Per Minute

**Electricity Use:** 61 Watts (excludes lights)

**Airflow Efficiency:** 59 Cubic Feet Per Minute Per Watt



Compact Fluorescent Lamps contain mercury.  For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

**72019**

**42" Oil Rubbed Bronze Finish**

Reversible Blades (Walnut/Family Oak)

Includes Light Kit with Opal Frosted Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 40 Watt G16 1/2 Lamps

**Airflow:** 2897 Cubic Feet Per Minute

**Electricity Use:** 53 Watts (excludes lights)

**Airflow Efficiency:** 55 Cubic Feet Per Minute Per Watt

**78764**

**42" Gun Metal Finish**

Reversible Blades (Black/Graphite)

Includes Light Kit with Opal Frosted Glass



**72473**

**42" Brushed Nickel Finish**

Reversible Blades (Beech/Wengue)

Includes Light Kit with Opal Frosted Glass



# Delancey LED

Highly-efficient DC motor and LED light kit take this modern style to the next level.

**72089**

**52" Brushed Chrome Finish**

Silver ABS Blades

Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Remote Control
- 6 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 5206 Cubic Feet Per Minute

**Electricity Use:** 32 Watts (excludes lights)

**Airflow Efficiency:** 163 Cubic Feet Per Minute Per Watt



## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72089	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	25000	22.8	\$1.92

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Delancey

A sleek, casual design and efficient DC motor combine style and performance.

**78001**

**52" Brushed Chrome Finish**

Silver ABS Blades

Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Remote Control
- 6 Fan Speeds
- Includes: (2) Medium (E26) Base, 13 Watt CFL Mini-Twists

**Airflow:** 5206 Cubic Feet Per Minute

**Electricity Use:** 32 Watts (excludes lights)

**Airflow Efficiency:** 163 Cubic Feet Per Minute Per Watt



# Troy

Sleek gun metal finish and high gloss black blades combine for a clean, modern aesthetic.

**72017**

**52" Gun Metal Finish**

High Gloss Black Blades

Includes Light Kit with Opal Frosted Glass


## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 13 Watt CFL Mini-Twists

**Airflow:** 5301 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 89 Cubic Feet Per Minute Per Watt



Compact Fluorescent Lamps contain mercury. (Hg) For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

# Bocca

Bring any modern space to life with this unique design featuring an integrated LED light kit.

72044

52" Gun Metal Finish

Reversible Blades (Applewood/Black)  
Includes Light Kit with Frosted Acrylic

## SPECIFICATIONS

- ¾" X 8" Down Rod
- Includes Remote Control
- 4 Fan Speeds
- Includes 17 Watt Integrated LED

**Airflow:** 5193 Cubic Feet Per Minute

**Electricity Use:** 64 Watts (excludes lights)

**Airflow Efficiency:** 81 Cubic Feet Per Minute Per Watt



INTEGRATED  
DIMMABLE  
LED



# Bendan LED

An integrated LED light kit and hammered accents give this fan a modern-day makeover.

72065

52" Brushed Nickel Finish

with Hammered Accents Catalpa Wood Blades  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Remote Control
- 4 Fan Speeds
- Includes 17.5 Watt Integrated LED

**Airflow:** 4452 Cubic Feet Per Minute

**Electricity Use:** 62 Watts (excludes lights)

**Airflow Efficiency:** 72 Cubic Feet Per Minute Per Watt



New!

INTEGRATED  
DIMMABLE  
LED



Hammered Accent  
Detail Shown

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72044	*	17	75	2700 (Warm White)	800	80	25000	22.8	\$2.05
72065	*	17.5	100	3000 (Warm White)	1250	80	25000	22.8	\$2.11

For a complete list of compatible dimmers, visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

\*Integrated LED Light Source

\*\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Bendan

Eye-catching tapered blades make this fan an ideal centerpiece in any large room.

72557

52" Satin Chrome Finish

Wengue Blades  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (1) R7 Base, 100 Watt Double-Ended Halogen Lamp

**Airflow:** 4478 Cubic Feet Per Minute

**Electricity Use:** 58 Watts (excludes lights)

**Airflow Efficiency:** 77 Cubic Feet Per Minute Per Watt



[www.westinghouselighting.com](http://www.westinghouselighting.com)

# Aerialist

Striking two blade design features a highly efficient DC motor.

**72016**

**52" Oil Brushed Bronze Finish**

Reversible Blades

(Applewood with Shaded Edge/Dark Walnut)

## SPECIFICATIONS

- Includes Remote Control
- 6 Fan Speeds

**Airflow:** 5661 Cubic Feet Per Minute

**Electricity Use:** 33 Watts (excludes lights)

**Airflow Efficiency:** 172 Cubic Feet Per Minute Per Watt





# Sparta

*Functional yet fashionable, this modern design infuses sophistication into any space.*

**78524**

**52" Brushed Nickel Finish**

*Weathered Maple Blades  
Includes Light Kit with Opal Glass*

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (1) Mini-Can (E11) Base,  
100 Watt Single-Ended Halogen Lamp

**Airflow:** 4292 Cubic Feet Per Minute

**Electricity Use:** 53 Watts (excludes lights)

**Airflow Efficiency:** 81 Cubic Feet Per Minute Per Watt



# Solana

*Sophisticated, cutting-edge look enhances modern décor.*

**72161**

**48" Brushed Nickel Finish**

*Wengue Blades  
Includes Light Kit with Opal Frosted Glass*

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base,  
60 Watt G16 1/2 Lamps

**Airflow:** 4698 Cubic Feet Per Minute

**Electricity Use:** 50 Watts (excludes lights)

**Airflow Efficiency:** 94 Cubic Feet Per Minute Per Watt



# Harmony

*Bring serenity to your home with this refined and balanced design.*

**72141**

**48" Brushed Nickel Finish**

*Weathered Maple Blades  
Includes Light Kit with Opal Frosted Glass*

## SPECIFICATIONS

- ¾" X 6" Down Rod
- Includes Pull Chains
- 4 Fan Speeds
- Includes: (2) Candelabra (E12) Base,  
40 Watt Torpedo Lamps

**Airflow:** 4611 Cubic Feet Per Minute

**Electricity Use:** 56 Watts (excludes lights)

**Airflow Efficiency:** 82 Cubic Feet Per Minute Per Watt



# Cumulus

All over white finish is fresh, bright, and modern.

**72598**

**48" White Finish**

Reversible Blades (White/White Washed Pine)  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- 3/4" X 10" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (1) Mini-Can (E11) Base, 75 Watt Single-Ended Halogen Lamp

**Airflow:** 4858 Cubic Feet Per Minute

**Electricity Use:** 53 Watts (excludes lights)

**Airflow Efficiency:** 92 Cubic Feet Per Minute Per Watt



# Lavada

Add a touch of transitional elegance to your space with this sleek, polished design.

**72474**

**48" Brushed Nickel Finish**

Reversible Blades (Dark Cherry/Applewood)  
Includes Light Kit with Frosted Opal Glass

## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) R7 Base, 100 Watt Double-Ended Halogen Lamp

**Airflow:** 4757 Cubic Feet Per Minute

**Electricity Use:** 52 Watts (excludes lights)

**Airflow Efficiency:** 91 Cubic Feet Per Minute Per Watt



# Arcadia

Classic details with a modern twist make this fan the perfect upgrade in any room.

**78775**  
**46" Brushed Nickel Finish**  
 Reversible Blades (Beech/Weathered Maple)  
 Includes Light Kit with Frosted White Alabaster Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 40 Watt G16 1/2 Lamps

**Airflow:** 1877 Cubic Feet Per Minute

**Electricity Use:** 50 Watts (excludes lights)

**Airflow Efficiency:** 37 Cubic Feet Per Minute Per Watt



**78691**  
**46" White Finish**  
 Reversible Blades  
 (Light Maple/White)  
 Includes Light Kit with Frosted White Alabaster Glass



# Vector Elite

*Dramatic contemporary details make an impressive statement.*

**78507**

**42" Brushed Nickel and Graphite Finish**

*Reversible Blades (Graphite/Silver)*

*Includes Light Kit with Brushed Nickel Spot Lights*

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (3) GU10 Base, 50 Watt MR16 Halogen Lamps

**Airflow:** 552 Cubic Feet Per Minute

**Electricity Use:** 53 Watts (excludes lights)

**Airflow Efficiency:** 10 Cubic Feet Per Minute Per Watt



# Elite

*Attractive details combine with impressive efficiency in this distinctive design.*

**78505**

**48" Brushed Nickel Finish**

*Beech Blades*

*Includes Light Kit with Brushed Nickel Spot Lights*

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (3) GU10 Base, 50 Watt MR16 Halogen Lamps

**Airflow:** 3723 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 63 Cubic Feet Per Minute Per Watt





# Xavier

This unique collection features adjustable spot lights, allowing for customizable illumination.

**7226565**

**44" Brushed Nickel Finish with Copper Accents**

Reversible Blades (Maple/Mahogany)  
Includes Light Kit with Spot Lights

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (3) GU10 Base, 50 Watt MR16 Halogen Lamps

**Airflow:** 4281 Cubic Feet Per Minute

**Electricity Use:** 64 Watts (excludes lights)

**Airflow Efficiency:** 67 Cubic Feet Per Minute Per Watt



# Xavier II

This distinctive design with adjustable spot lights brightens and cools any large space.

**7234265**

**52" Brushed Nickel Finish with Gun Metal Accents**

Reversible Blades (Graphite/Weathered Maple)  
Includes Light Kit with Spot Lights

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (3) GU10 Base, 50 Watt MR16 Halogen Lamps

**Airflow:** 4476 Cubic Feet Per Minute

**Electricity Use:** 65 Watts (excludes lights)

**Airflow Efficiency:** 69 Cubic Feet Per Minute Per Watt



# Panorama

A stunning light kit trimmed in luminous chrome makes this design the center of attention in any room.

**72559**

**52" Chrome Finish**

Reversible Blades (High Gloss White/Black)  
Includes Light Kit with Opal Frosted Glass Shades

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (4) Medium (E26) Base, 14 Watt CFL Mini-Twists

**Airflow:** 1191 Cubic Feet Per Minute

**Electricity Use:** 62 Watts (excludes lights)

**Airflow Efficiency:** 19 Cubic Feet Per Minute Per Watt



Compact Fluorescent Lamps contain mercury. (Hg) For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

# Roundabout

Whimsical details are balanced by clean, modern lines in this cheerful design.

**72475**

**30" Brushed Nickel Finish**

Reversible Blades (Multi-Color/White)  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 40 Watt G16 1/2 Lamps

**Airflow:** 2083 Cubic Feet Per Minute

**Electricity Use:** 43 Watts (excludes lights)

**Airflow Efficiency:** 48 Cubic Feet Per Minute Per Watt



# Turbo Swirl CFL

A sleek, trendy design that is sure to boost any room's ambience.

**72261**

**30" Gun Metal Finish**

Black Blades  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Medium (E26) Base, 13 Watt CFL Mini-Twist

**Airflow:** 2564 Cubic Feet Per Minute

**Electricity Use:** 54 Watts (excludes lights)

**Airflow Efficiency:** 47 Cubic Feet Per Minute Per Watt



Compact Fluorescent Lamps contain mercury. (Hg) For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

# Turbo Swirl LED

A sleek, trendy design that is sure to boost any room's ambience.

**72092**

**30" Gun Metal Finish**

Black Blades  
Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Medium (E26) Base, 9 Watt Omni LED Lamp

**Airflow:** 2564 Cubic Feet Per Minute

**Electricity Use:** 54 Watts (excludes lights)

**Airflow Efficiency:** 47 Cubic Feet Per Minute Per Watt



## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72092	1	9	60	3000 (Warm White)	800	80	15000	13.6	\$1.08

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Turbo Swirl

Compact designs supply powerful air circulation with sleek finishes and curvy blades.

**7824865**  
**30" Antique Brass Finish**  
Walnut Blades  
Includes Light Kit  
with Opal Frosted Glass



## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Candelabra (E12) Base, 60 Watt G16 1/2 Lamp

**Airflow:** 369 Cubic Feet Per Minute

**Electricity Use:** 54 Watts (excludes lights)

**Airflow Efficiency:** 7 Cubic Feet Per Minute Per Watt



**7814565**  
**30" White Finish**  
White Blades  
Includes Light Kit with Opal Frosted Glass



**7814465**  
**30" Brushed Aluminum Finish**  
Light Maple Blades  
Includes Light Kit  
with Opal Frosted Glass





# Wengue

Casual yet bold, these designs add allure to any setting.

**72472**

**30" White Finish**

Reversible Blades (White/Beech)

Includes Light Kit with Opal Frosted Glass



## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 40 Watt G16 1/2 Lamps

**Airflow:** 1816 Cubic Feet Per Minute

**Electricity Use:** 34 Watts (excludes lights)

**Airflow Efficiency:** 53 Cubic Feet Per Minute Per Watt

**78763**

**30" Chrome Finish**

Reversible Blades (Wengue/Beech)

Includes Light Kit with Opal Frosted Glass



**72245**

**30" Espresso Finish**

Reversible Blades

(Espresso/Dark Cherry)

Includes Light Kit with Opal Frosted Glass





# Quince

An ample light kit brightens, while six blades ensure optimal airflow in smaller-sized rooms.

**72243**

**24" Gun Metal Finish**

Reversible Blades (Black/Graphite)  
Includes Light Kit  
with Opal Frosted Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 40 Watt G16 1/2 Lamps

**Airflow:** 1270 Cubic Feet Per Minute

**Electricity Use:** 28 Watts (excludes lights)

**Airflow Efficiency:** 45 Cubic Feet Per Minute Per Watt

**72471**

**24" White Finish**

Reversible Blades (White/Beech)  
Includes Light Kit  
with Opal Frosted Glass



**78631**

**24" Chrome Finish**

Reversible Blades  
(Wengue/Beech)  
Includes Light Kit  
with Opal Frosted Glass



# Origami

This compact, propeller-styled fan brings a nautical touch to any room.

**72229**

**24" Espresso Finish**

Reversible Blades (Espresso/Applewood)  
Includes Light Kit with Opal Frosted Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Candelabra (E12) Base, 60 Watt G16 1/2 Lamp

**Airflow:** 1174 Cubic Feet Per Minute

**Electricity Use:** 29 Watts (excludes lights)

**Airflow Efficiency:** 40 Cubic Feet Per Minute Per Watt

**78644**

**24" Chrome Finish**

Reversible Blades (Wengue/Beech)  
Includes Light Kit with Opal Frosted Glass





# Westinghouse

INNOVATION YOU CAN BE SURE OF



## TRADITIONAL CEILING FANS

Known for their classic and distinctive designs, traditional fans have endured through the years. Available in a multitude of finishes, including antique brass, oil brushed bronze and brushed nickel, we offer styles to complement all types of living spaces.

# Thurlow


*Distressed wood and industrial-style details add vintage appeal.*

**72076**  
**54" Weathered Bronze Finish**  
 Reversible Blades  
 (Driftwood/Reclaimed Hickory)

**SPECIFICATIONS**

- 3/4" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds

**Airflow:** 5045 Cubic Feet Per Minute  
**Electricity Use:** 61 Watts  
**Airflow Efficiency:** 83 Cubic Feet Per Minute Per Watt



*Driftwood  
Finish*



*Reclaimed Hickory  
Finish*

# Aiden

*With its traditional style and luminous finishes, the Aiden is an ideal upgrade to any space.*

**72036**  
**52" Brushed Nickel Finish**  
 Reversible Blades  
 (Rich Walnut/Bird's Eye Maple)

**SPECIFICATIONS**

- 3/4" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds

**Airflow:** 3585 Cubic Feet Per Minute  
**Electricity Use:** 54 Watts  
**Airflow Efficiency:** 66 Cubic Feet Per Minute Per Watt



**72037**  
**52" Oil Brushed Bronze Finish**  
 Reversible Blades (Dark Cherry/Mahogany)



# Tulsa LED

Add comfort to your home with these grand designs that will never go out of style.

**72094**

**52" Brushed Nickel Finish**

Reversible Blades

(Rich Walnut/Bird's Eye Maple)

Includes Light Kit with White Alabaster Glass



## SPECIFICATIONS

- 3/4" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 3315 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 57 Cubic Feet Per Minute Per Watt

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72094	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$1.92

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Tulsa

Add comfort to your home with these grand designs that will never go out of style.

**72006**

**52" Oil Brushed Bronze Finish**

Reversible Blades

(Dark Cherry/Mahogany)

Includes Light Kit with Amber Alabaster Glass



## SPECIFICATIONS

- 3/4" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 13 Watt CFL Mini-Twists

**Airflow:** 3315 Cubic Feet Per Minute

**Electricity Use:** 58 Watts (excludes lights)

**Airflow Efficiency:** 57 Cubic Feet Per Minute Per Watt

**72005**

**52" Brushed Nickel Finish**

Reversible Blades

(Rich Walnut/Bird's Eye Maple)

Includes Light Kit

with White Alabaster Glass



Compact Fluorescent Lamps contain mercury. (Hg) For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).



# Anderson

*Refined and sophisticated, this polished design is perfect for larger spaces.*

**72000**

**52" Polished Nickel Finish**

*Reversible Blades (Weathered Maple/Beech)  
Includes Light Kit with White Alabaster Glass*

## SPECIFICATIONS


- 3/4" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 13 Watt CFL Mini-Twists

**Airflow:** 4852 Cubic Feet Per Minute

**Electricity Use:** 58 Watts (excludes lights)

**Airflow Efficiency:** 84 Cubic Feet Per Minute Per Watt



Compact Fluorescent Lamps contain mercury.  For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

# Fairview

*Distinctive, traditional accents evoke timeless style.*

**78400**

**52" Brushed Nickel Finish**

*Reversible Blades (Weathered Maple/Dark Cherry)  
Includes Light Kit with Frosted Glass*

## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Remote Control
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 60 Watt G16 1/2 Lamps

**Airflow:** 3875 Cubic Feet Per Minute

**Electricity Use:** 57 Watts (excludes lights)

**Airflow Efficiency:** 68 Cubic Feet Per Minute Per Watt



**78399**

**52" Oil Rubbed Bronze Finish**

*Reversible Blades (Dark Cherry/Walnut)  
Includes Light Kit with Frosted Glass*



# Swirl

Handsome designs shed generous, even light, adding comfort and ambience to larger rooms.

**7852165**

**52" Brushed Nickel Finish**

Reversible Blades (Rosewood/Light Maple)  
Includes Light Kit with Frosted Swirl Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (4) Candelabra (E12) Base, 40 Watt Torpedo Lamps

**Airflow:** 4259 Cubic Feet Per Minute

**Electricity Use:** 66 Watts (excludes lights)

**Airflow Efficiency:** 65 Cubic Feet Per Minute Per Watt

**7856865**

**52" Rustic Bronze Finish**

Reversible Blades (Mahogany/Rich Walnut)  
Includes Light Kit with Frosted Swirl Glass



# Vintage II

A classic design that provides enduring style.

**7839165**

**52" Brushed Nickel Finish**

Reversible Blades (Rosewood/Light Maple)  
Includes Light Kit with White Alabaster Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 60 Watt G16 1/2 Lamps

**Airflow:** 3787 Cubic Feet Per Minute

**Electricity Use:** 61 Watts (excludes lights)

**Airflow Efficiency:** 62 Cubic Feet Per Minute Per Watt

# Vintage

Timeless and classic, these designs are ideal for traditional homes.



**72079**

**52" Oil Rubbed Bronze Finish**

Reversible Blades (Rosewood/Light Maple)  
Includes Light Kit with Frosted Ribbed Glass



**7867865**

**52" Brushed Nickel Finish**

Reversible Blades (Rosewood/Light Maple)  
Includes Light Kit with Frosted Ribbed Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- Includes: (3) Candelabra (E12) Base, 60 Watt Torpedo Lamps

**Airflow:** 3835 Cubic Feet Per Minute

**Electricity Use:** 64 Watts (excludes lights)

**Airflow Efficiency:** 60 Cubic Feet Per Minute Per Watt



**7862765**

**52" White Finish**

Reversible Blades (White/White Washed Pine)  
Includes Light Kit with Frosted Ribbed Glass



**7804365**

**52" Polished Brass Finish**

Reversible Blades (Walnut/Oak)  
Includes Light Kit with Clear Ribbed Glass





# Goodwin

Infuse a touch of rustic elegance in any room.

**72014**

**52" Oil Brushed Bronze Finish**

*Reversible Blades*

*(Applewood with Shaded Edge/Dark Walnut)*  
Includes Light Kit with Amber Mist Glass


## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 13 Watt CFL Mini-Twists

**Airflow:** 5015 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 84 Cubic Feet Per Minute Per Watt



(Hg)

Compact Fluorescent Lamps contain mercury. (Hg) For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

# Richboro SE

Bring any space to life with this attractive design that matches any décor.

**7877365**

**42" Brushed Nickel Finish**

*Reversible Blades (Rosewood/Light Maple)*

*Includes Light Kit with Frosted White Alabaster Glass*

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 60 Watt G16 1/2 Lamps

**Airflow:** 3112 Cubic Feet Per Minute

**Electricity Use:** 48 Watts (excludes lights)

**Airflow Efficiency:** 65 Cubic Feet Per Minute Per Watt



# Newtown

Water glass shades add a charming twist to this traditional design.

**7843565**

**42" Brushed Nickel Finish**

*Reversible Blades*

*(Light Maple/Bird's Eye Maple)*

*Includes Light Kit with Water Glass*

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (3) Candelabra (E12) Base, 60 Watt Torpedo Lamps

**Airflow:** 3361 Cubic Feet Per Minute

**Electricity Use:** 57 Watts (excludes lights)

**Airflow Efficiency:** 59 Cubic Feet Per Minute Per Watt





# Cassidy

With its compact design and sleek details, the Cassidy is ideal for smaller spaces.

**72032**

**36" Brushed Nickel Finish**

Reversible Blades (Wengue/Silver)

Includes Light Kit with Opal Frosted Glass

## SPECIFICATIONS

- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 40 Watt G16 1/2 Lamps

**Airflow:** 2353 Cubic Feet Per Minute

**Electricity Use:** 43 Watts (excludes lights)

**Airflow Efficiency:** 55 Cubic Feet Per Minute Per Watt



# Carolina LED

Sculpted details and rich wood finishes create this statement-making design.

**72096**

**52" Oil Rubbed Bronze Finish**

Reversible Blades (Applewood/Cherry)

Includes Light Kit with Amber Alabaster Glass

## SPECIFICATIONS

- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Medium (E26) Base, 8 Watt T7 LED Lamps

**Airflow:** 3361 Cubic Feet Per Minute

**Electricity Use:** 52 Watts (excludes lights)

**Airflow Efficiency:** 64 Cubic Feet Per Minute Per Watt



**72097**

**52" Brushed Nickel Finish**

Reversible Blades

(Rich Walnut/Bird's Eye Maple)

Includes Light Kit with White Alabaster Glass



## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72096	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$1.92
72097	2	16	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$1.92

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Sumter LED

Add a touch of traditional sophistication to your home.

**72131**

**52" Classic Bronze Finish**

Reversible Blades (Applewood with Shaded Edge/Dark Cherry)  
Includes Light Kit with Amber Alabaster Glass

**SPECIFICATIONS**

- Includes Pull Chains
- 3 Fan Speeds
- **72131** Includes: (2) Medium (E26) Base, 10 Watt Omni LED Lamps
- **72132** Includes: (2) Medium (E26) Base, 9 Watt Omni LED Lamps

**Airflow:** 354 Cubic Feet Per Minute

**Electricity Use:** 58 Watts (excludes lights)

**Airflow Efficiency:** 6 Cubic Feet Per Minute Per Watt



**72132**

**52" Brushed Nickel Finish**

Reversible Blades (Weathered Maple/Beech)  
Includes Light Kit with White Alabaster Glass

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72131	2	20	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$2.16
72132	2	18	120 (2 x 60)	3000 (Warm White)	1600	80	15000	13.6	\$2.16

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Contempra IV

Ideal for larger rooms with lower ceilings, these traditional designs provide ample illumination and powerful air circulation.

**72162**

**52" Oil Rubbed Bronze Finish**

Reversible Blades (Dark Cherry/Walnut)  
Includes Light Kit with Frosted Ribbed Glass

**SPECIFICATIONS**

- Includes Pull Chains
- 3 Fan Speeds
- Includes: (4) Candelabra (E12) Base, 40 Watt Torpedo Lamps

**Airflow:** 3341 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 57 Cubic Feet Per Minute Per Watt



# Contempra IV (cont.)

72164

**52" White Finish**

Reversible Blades (White/White Washed Pine)  
Includes Light Kit with Frosted Ribbed Glass

## SPECIFICATIONS

- Includes Pull Chains
- 3 Fan Speeds
- Includes: (4) Candelabra (E12) Base, 40 Watt Torpedo Lamps

**Airflow:** 3341 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 57 Cubic Feet Per Minute Per Watt



**New!**



72165

**52" Polished Brass Finish**

Reversible Blades (Walnut/Oak)  
Includes Light Kit with Clear Ribbed Glass



**New!**



72163

**52" Antique Brass Finish**

Reversible Blades (Oak/Walnut)  
Includes Light Kit with Frosted Ribbed Glass



**New!**



72160

**52" Brushed Nickel Finish**

Reversible Blades (Rosewood/Bird's Eye Maple)  
Includes Light Kit with Frosted Ribbed Glass



# Hadley

Brighten any small room with this stylish, classic design.

**72128**

**42" Brushed Nickel Finish**

Reversible Blades (Dark Cherry/Rosewood)  
Includes Light Kit with White Alabaster Glass

## SPECIFICATIONS

- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 60 Watt G16 1/2 Lamps

**Airflow:** 2788 Cubic Feet Per Minute

**Electricity Use:** 50 Watts (excludes lights)

**Airflow Efficiency:** 56 Cubic Feet Per Minute Per Watt



**72130**

**42" Oil Rubbed Bronze Finish**

Reversible Blades (Applewood/Cherry)  
Includes Light Kit with White Alabaster Glass



# Contempra Trio

Hugger designs in popular finishes are perfect for rooms with lower ceilings.

**72159**

**42" Brushed Nickel Finish**

Reversible Blades (Rosewood/Bird's Eye Maple)  
Includes Light Kit with Frosted Glass

## SPECIFICATIONS

- Includes Pull Chains
- 3 Fan Speeds
- Includes: (3) Candelabra (E12) Base, 60 Watt Torpedo Lamps

**Airflow:** 2829 Cubic Feet Per Minute

**Electricity Use:** 56 Watts (excludes lights)

**Airflow Efficiency:** 51 Cubic Feet Per Minute Per Watt





# Contempra Trio (cont.)

Hugger designs in popular finishes are perfect for rooms with lower ceilings.

## SPECIFICATIONS

- Includes Pull Chains
- 3 Fan Speeds
- Includes: (3) Candelabra (E12) Base, 60 Watt Torpedo Lamps

**Airflow:** 2829 Cubic Feet Per Minute

**Electricity Use:** 56 Watts (excludes lights)

**Airflow Efficiency:** 51 Cubic Feet Per Minute Per Watt



**New!**

**72149**  
**42" Oil Rubbed Bronze Finish**  
 Reversible Blades (Dark Cherry/Walnut)  
 Includes Light Kit with Frosted Glass



**New!**

**72157**  
**42" Antique Brass Finish**  
 Reversible Blades (Oak/Walnut)  
 Includes Light Kit with Frosted Glass



**New!**

**72151**  
**42" Satin Brass Finish**  
 Reversible Blades (Walnut/Maple)  
 Includes Light Kit with Frosted Glass



**New!**

**72150**  
**42" White Finish**  
 Reversible Blades (White/White Washed Pine)  
 Includes Light Kit with Frosted Glass



# Casanova

Add comfort to rooms with lower ceilings with this classic hugger fan.

**78053**

**52" White Finish**

Reversible Blades  
(White/White Washed Pine)


## SPECIFICATIONS

- Includes Pull Chains
- 3 Fan Speeds

**Airflow:** 3427 Cubic Feet Per Minute

**Electricity Use:** 59 Watts

**Airflow Efficiency:** 58 Cubic Feet Per Minute Per Watt



# Casanova Supreme

Traditional style brings comfort to any room.

**72136**

**42" Antique Brass Finish**

Reversible Blades (Oak/Walnut)  
Includes Light Kit with Opal Schoolhouse Glass

## SPECIFICATIONS

- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Candelabra (E12) Base, 60 Watt G16 1/2 Lamp

**Airflow:** 1316 Cubic Feet Per Minute

**Electricity Use:** 49 Watts (excludes lights)

**Airflow Efficiency:** 27 Cubic Feet Per Minute Per Watt



**72144**

**42" White Finish**

Reversible Blades (White/White Washed Pine)  
Includes Light Kit with Opal Schoolhouse Glass

**72138**

**42" Polished Brass Finish**

Reversible Blades (Walnut/Oak)  
Includes Light Kit with Opal Schoolhouse Glass



# Petite

Classic design details come together beautifully in a compact fan for smaller spaces.

**72158**

**30" Antique Brass Finish**

*Reversible Blades (Walnut/Oak)*

*Includes Light Kit with Opal Mushroom Glass*



## SPECIFICATIONS

- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Candelabra (E12) Base, 60 Watt G16 1/2 Lamp

**Airflow:** 2027 Cubic Feet Per Minute

**Electricity Use:** 46 Watts (excludes lights)

**Airflow Efficiency:** 44 Cubic Feet Per Minute Per Watt

**New!**



**72135**

**30" White Finish**

*Reversible Blades (White/White Washed Pine)*

*Includes Light Kit with Opal Mushroom Glass*



**72133**

**30" Brushed Nickel Finish**

*Reversible Blades (Rosewood/Light Maple)*

*Includes Light Kit with Opal Mushroom Glass*








# Westinghouse

INNOVATION YOU CAN BE SURE OF



## OUTDOOR CEILING FANS

Westinghouse ceiling fans designed for patios, verandahs and gazebos create ambience and style in any outdoor living space. Our indoor/outdoor ceiling fans are suitable for both indoor and outdoor locations.





# Brentford

Remarkable attention to detail complements an upscale, lantern-style light kit to create a stunning work of art.

**78000**

**52" Aged Walnut Finish**

Reversible ABS Blades  
(Dark Cherry Shaded Edges/Walnut)  
Includes Light Fixture with Clear Seeded Glass



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (3) Candelabra (E12) Base, 40 Watt Torpedo Lamps

**Airflow:** 4522 Cubic Feet Per Minute

**Electricity Use:** 56 Watts (excludes lights)

**Airflow Efficiency:** 81 Cubic Feet Per Minute Per Watt



Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.

# Great Falls

A touch of rustic style, a hint of nautical flair and a dash of modern technology are a perfect combination for any living space.

**72043**

**52" Oil Rubbed Bronze Finish**

Dark Walnut ABS Blades  
Includes Light Fixture with Frosted Amber Glass



WET LOCATION RATED

## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Medium (E26) Base, 10 Watt Omni LED Lamp

**Airflow:** 4070 Cubic Feet Per Minute

**Electricity Use:** 55 Watts (excludes lights)

**Airflow Efficiency:** 74 Cubic Feet Per Minute Per Watt

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72043	1	10	60	3000 (Warm White)	800	80	15000	13.6	\$1.08

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Lafayette LED

*Weathered hues and a lantern light kit add rustic character and cozy ambience.*

**72098**

**52" Weathered Iron Finish**

*Light Oak ABS Blades*

*Includes Light Fixture with Yellow Alabaster Glass*

## SPECIFICATIONS

- ¾" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Medium (E26) Base, 9 Watt Omni LED Lamp

**Airflow:** 4588 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 78 Cubic Feet Per Minute Per Watt



WET LOCATION RATED

## LED LIGHT SOURCE SPECIFICATIONS

Item No.	Number of Lamps	Total Energy Used (Watts)	Equiv. Incand. Wattage	Light Appearance (Kelvin)	Total Lumens	CRI	Average Rated Hours	Life in Years*	Total Est. Yearly Energy Cost**
72098	1	9	60	2700 (Warm White)	800	80	25000	22.8	\$1.08

\*Based on 3hrs./day \*\*Based on 3hrs./day 11¢/kWh

# Lafayette

*Timeless details and a unique lantern light kit are perfect for any traditional outdoor setting.*

**7877865**

**52" Weathered Iron Finish**

*Light Oak ABS Blades*

*Includes Light Fixture with Yellow Alabaster Glass*

## SPECIFICATIONS

- ¾" X 6" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Medium (E26) Base, 13 Watt CFL Mini-Twist

**Airflow:** 4588 Cubic Feet Per Minute

**Electricity Use:** 59 Watts (excludes lights)

**Airflow Efficiency:** 77 Cubic Feet Per Minute Per Watt



WET LOCATION RATED

Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

# Comet (Outdoor)

A sleek, informal design is an ideal choice for adding casual style to outdoor living spaces.

**72007**

**52" Espresso Finish**

*Espresso ABS Blades*

*Includes Light Fixture with Frosted Glass*



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (2) Candelabra (E12) Base, 40 Watt Torpedo Lamps

**Airflow:** 4075 Cubic Feet Per Minute

**Electricity Use:** 61 Watts (excludes lights)

**Airflow Efficiency:** 67 Cubic Feet Per Minute Per Watt



**72008**

**52" White Finish**

*White ABS Blades*

*Includes Light Fixture with Frosted Glass*



# Oasis

Mahogany leaf blades add a relaxing, tropical feel to any indoor or outdoor living space.

**7861965**

**48" Oil Rubbed Bronze Finish**

*Mahogany Leaf ABS Blades*

*Includes Light Fixture with Yellow Alabaster Glass*



## SPECIFICATIONS

- 3/4" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds
- Includes: (1) Candelabra (E12) Base, 60 Watt G16 1/2 Lamp

**Airflow:** 3983 Cubic Feet Per Minute

**Electricity Use:** 50 Watts (excludes lights)

**Airflow Efficiency:** 80 Cubic Feet Per Minute Per Watt





# Westinghouse

INNOVATION YOU CAN BE SURE OF



## INDUSTRIAL & CONTRACTOR CEILING FANS

Commercial environments require durable, reliable ceiling fans. Westinghouse industrial and contractor ceiling fans provide the uncompromising quality you expect from an international brand.



# Urban Gale

*Sleek, industrial look designed for residential settings with high ceilings.*

## SPECIFICATIONS

- ½" X 12" Down Rod
- Includes Remote Control
- 3 Fan Speeds

**Airflow:** 5734 Cubic Feet Per Minute

**Electricity Use:** 66 Watts (excludes lights)

**Airflow Efficiency:** 87 Cubic Feet Per Minute Per Watt

**72021**

**52" White Finish**

*White ABS Blades*



**72020**

**52" Brushed Nickel Finish**

*Black ABS Blades*

# Industrial

*Resilient, dependable designs for industrial and commercial environments.*

## SPECIFICATIONS

- 15 Year Limited Warranty
- ½" X 12" Down Rod
- Includes Wall Control
- 4 Fan Speeds

**Airflow:** 6045 Cubic Feet Per Minute

**Electricity Use:** 64 Watts (excludes lights)

**Airflow Efficiency:** 94 Cubic Feet Per Minute Per Watt

**78003**

**56" Brushed Nickel Finish**

*Black Steel Blades*

*Ball Hanger Installation System*



**78614**

**56" Brushed Nickel Finish**

*Brushed Nickel Finish Steel Blades*

*Ball Hanger Installation System*

## SPECIFICATIONS

- 15 Year Limited Warranty
- ½" X 12" Down Rod
- Includes Wall Control
- 5 Fan Speeds

**Airflow:** 5973 Cubic Feet Per Minute

**Electricity Use:** 62 Watts (excludes lights)

**Airflow Efficiency:** 97 Cubic Feet Per Minute Per Watt

**CAUTION!** All Westinghouse Urban Gale and Industrial fans must be installed with blades at least 10 feet from the floor.

# Industrial

Resilient, dependable designs for industrial and commercial environments.

**78127**  
**56" White Finish**  
 White Steel Blades  
 Ball Hanger Installation System



## SPECIFICATIONS

- 15 Year Limited Warranty
- ½" X 12" Down Rod
- Includes Wall Control
- 5 Fan Speeds

**Airflow:** 5973 Cubic Feet Per Minute

**Electricity Use:** 62 Watts (excludes lights)

**Airflow Efficiency:** 96 Cubic Feet Per Minute Per Watt

**78409**  
**56" White Finish**  
 White Steel Blades  
 J Hook Installation System



J-Hook  
 Installation System

# Contractor's Choice

Traditional and durable, this design is ideal for any décor.

**78024**  
**52" White Finish**  
 White Blades



## SPECIFICATIONS


- ¾" X 4" Down Rod
- Includes Pull Chains
- 3 Fan Speeds

**Airflow:** 4099 Cubic Feet Per Minute

**Electricity Use:** 65 Watts (excludes lights)

**Airflow Efficiency:** 63 Cubic Feet Per Minute Per Watt

**CAUTION!** All Westinghouse Urban Gale and Industrial fans must be installed with blades at least 10 feet from the floor.



- A. Ceiling to bottom of blade
- B. Ceiling to bottom of switch housing
- C. Ceiling to bottom of canopy
- D. Width of motor housing
- E. Width of canopy
- F. Ceiling to bottom of light kit

## CEILING FAN SPECIFICATIONS - DIMENSIONS

Family Name	Size of Down Rod Included	A	B	C	D	E	F
Aerialist	N/A	18.50"	N/A	N/A	7.77"	N/A	N/A
Aiden	3/4" X 6"	11.61"	14.45"	2.44"	11.42"	5.20"	N/A
Alloy 42"	3/4" X 4"	6.38"	11.00"	2.50"	6.75"	5.13"	11.75"
Alloy 52"	3/4" X 4"	8.07"	11.42"	2.44"	7.05"	5.12"	13.19"
Alloy II	3/4" X 4"	10.00"	11.42"	2.44"	7.09"	5.12"	13.90"
Alloy LED	3/4" X 4"	8.07"	11.42"	2.44"	7.05"	5.12"	13.19"
Alta Vista	3/4" X 4"	10.83"	8.39"	2.44"	7.87"	5.12"	13.70"
Anderson	3/4" X 6"	13.13"	15.00"	2.20"	11.02"	5.98"	19.25"
Arcadia	3/4" X 4"	9.38"	11.00"	2.00"	9.75"	5.88"	14.00"
Bendan	3/4" X 4"	11.42"	7.87"	2.44"	10.24"	5.12"	14.17"
Bendan LED	3/4" X 4"	11.42"	7.87"	2.44"	10.24"	5.12"	14.17"
Bocca	3/4" X 8"	15.04"	N/A	2.28"	11.10"	5.91"	18.11"
Bolton	3/4" X 4"	9.25"	12.20"	2.36"	11.02"	5.12"	14.37"
Brentford	3/4" X 4"	9.96"	11.65"	2.06"	12.36"	5.83"	18.78"
Carolina LED	N/A	6.88"	9.75"	N/A	11.10"	N/A	13.75"
Casanova	N/A	8.00"	8.50"	N/A	11.00"	N/A	N/A
Casanova Supreme	N/A	7.25"	8.50"	N/A	8.75"	N/A	12.50"
Cassidy	3/4" X 4"	11.22"	11.81"	2.09"	8.58"	5.12"	16.54"
Castle	3/4" X 6"	11.43"	12.63"	2.40"	10.49"	5.13"	15.98"
Castle LED	3/4" X 6"	11.43"	12.63"	2.40"	10.49"	5.13"	15.98"
Cayuga	3/4" X 6"	13.78"	11.54"	2.56"	10.63"	5.12"	17.13"
Comet (Outdoor)	3/4" X 4"	11.00"	12.60"	2.40"	11.30"	5.10"	14.40"
Comet	3/4" X 4"	11.88"	14.25"	2.25"	11.50"	5.13"	14.25"
Contempra IV	N/A	7.13"	8.13"	N/A	11.50"	N/A	13.00"
Contempra Trio	N/A	5.88"	7.50"	N/A	10.38"	N/A	13.38"
Contractor's Choice	3/4" X 4"	10.25"	11.25"	2.25"	9.00"	5.25"	N/A
Cumulus	3/4" X 10"	15.93"	19.30"	2.75"	7.28"	5.20"	21.30"
Delancey	3/4" X 4"	12.00"	9.45"	2.06"	7.87"	5.98"	16.14"
Delancey LED	3/4" X 4"	12.00"	9.45"	2.05"	7.87"	5.98"	16.14"
Desoto	3/4" X 6"	13.39"	13.78"	2.56"	8.27"	5.12"	15.75"
Elite	3/4" X 4"	9.63"	12.63"	2.13"	9.00"	5.25"	16.63"
Fairview	3/4" X 4"	12.25"	13.00"	2.38"	11.00"	5.13"	18.88"
Goodwin	3/4" X 4.5"	11.54"	13.39"	2.05"	9.53"	5.83"	17.32"
Great Falls	3/4" X 4"	10.75"	12.76"	2.72"	7.87"	5.20"	20.08"
Hadley	N/A	5.13"	6.75"	N/A	8.46"	N/A	10.75"
Harmony	3/4" X 6"	10.63"	12.75"	2.00"	7.50"	6.00"	17.13"
Industrial	1/2" X 12"	17.32"	15.55"	2.44"	7.72"	5.13"	N/A
Industrial (78409)	1/2" X 12"	18.50"	17.32"	4.02"	7.72"	5.71"	N/A
Lafayette	3/4" X 6"	15.50"	16.13"	2.38"	12.25"	5.13"	24.00"
Lafayette LED	3/4" X 6"	15.50"	16.13"	2.38"	12.25"	5.13"	24.00"
Lavada	3/4" X 4"	8.07"	11.42"	2.07"	7.87"	6.14"	12.60"
Newtown	3/4" X 4"	11.38"	12.63"	2.38"	10.00"	5.13"	17.75"
Oasis	3/4" X 4"	13.63"	13.38"	2.38"	9.00"	5.13"	18.75"
Origami	3/4" X 4"	7.88"	10.00"	2.50"	6.75"	5.13"	14.75"
Panorama	3/4" X 4"	12.62"	9.00"	2.50"	10.75"	5.12"	15.87"
Petite	N/A	6.75"	8.00"	N/A	9.00"	N/A	12.00"
Quince	3/4" X 4"	9.00"	10.38"	2.50"	6.75"	5.13"	12.13"
Richboro SE	3/4" X 4"	12.25"	18.13"	2.25"	8.63"	5.13"	19.25"
Roundabout	3/4" X 4"	11.42"	13.75"	2.36"	7.68"	5.12"	15.92"
Solana	3/4" X 4"	10.75"	13.00"	2.00"	7.63"	6.25"	17.38"
Sparta	3/4" X 4"	10.70"	11.60"	2.10"	9.10"	5.86"	13.00"
Sumter LED	N/A	6.00"	7.87"	N/A	11.42"	N/A	14.20"
Swirl	3/4" X 4"	13.50"	12.00"	2.25"	12.00"	5.25"	18.00"
Techno	3/4" X 4"	9.13"	11.02"	2.06"	8.39"	6.14"	12.40"
Techno II	3/4" X 4"	11.02"	11.81"	2.06"	8.27"	5.86"	13.39"
Thurlow	3/4" X 6"	14.76"	16.93"	2.56"	8.66"	5.12"	13.27"
Troy	3/4" X 4"	12.50"	11.54"	2.06"	8.08"	6.14"	16.54"
Tulsa	3/4" X 6"	11.63"	14.88"	2.20"	11.50"	5.98"	20.25"
Tulsa LED	3/4" X 6"	11.63"	14.88"	2.20"	11.50"	5.98"	20.25"
Turbo Swirl	3/4" X 4"	10.00"	11.50"	2.25"	7.00"	5.00"	14.50"
Turbo Swirl CFL	3/4" X 4"	10.00"	11.50"	2.25"	7.00"	5.00"	16.50"
Turbo Swirl LED	3/4" X 4"	10.00"	11.50"	2.25"	7.00"	5.00"	16.50"
Urban Gale	1/2" X 12"	18.11"	15.75"	2.44"	18.90"	5.12"	N/A
Vector Elite	3/4" X 4"	7.00"	11.25"	2.13"	10.38"	5.13"	15.50"
Vintage	3/4" X 4"	10.87"	12.92"	2.41"	11.02"	5.12"	18.43"
Vintage II	3/4" X 4"	11.38"	13.25"	2.38"	11.13"	5.13"	19.25"
Wengue	3/4" X 4"	9.00"	10.38"	2.50"	6.75"	5.13"	12.13"
Xavier	3/4" X 4"	16.00"	17.50"	2.00"	10.00"	5.00"	22.50"
Xavier II	3/4" X 4"	16.00"	17.50"	2.00"	10.00"	5.00"	22.50"
Zander	1/2" X 6"	11.88"	14.25"	2.20"	10.26"	5.98"	16.50"
Zephyr	3/4" X 6"	13.18"	11.93"	2.56"	9.84"	5.12"	16.90"

If a Combo Style Fan with a 4" Down Rod is Installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).  
 If a Combo Style Fan with a 6" Down Rod is Installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

## CEILING FAN SPECIFICATIONS

Family Name	Page #	Size	Number of Blades	Blade Material	Blade Pitch	Motor Type and Size	Reverse Airflow	Capacitor Type	Number of Fan Speeds	Slope Angle
Aerialist	112	52"	2	Plywood	15°	DC Motor 125S	Yes	N/A	6	N/A
Aiden	123	52"	5	MDF	12°	Silicon Steel 153mm x 15mm	Yes	Triple	3	20°
Alloy 42"	109	42"	3	MDF	13°	Silicon Steel 153mm x 10mm	Yes	Dual	3	18°
Alloy 52"	109	52"	3	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	18°
Alloy II	108	52"	6	Plywood	10°	Silicon Steel 153mm x 17mm	Yes	Triple	3	18°
Alloy LED	108	52"	3	Plywood	13°	Silicon Steel 153mm x 17mm	Yes	Triple	3	18°
Alta Vista	106	52"	3	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Dual	4	N/A
Anderson	125	52"	5	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	20°
Arcadia	115	46"	3	Plywood	12°	Silicon Steel 153mm x 12mm	Yes	Triple	3	20°
Bendan	111	52"	5	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Dual	3	N/A
Bendan LED	111	52"	5	Wood	12°	Silicon Steel 153mm x 17mm	Yes	Dual	4	N/A
Bocca	111	52"	4	Plywood	12°	Silicon Steel 153mm x 18mm	Yes	Single	4	N/A
Bolton	105	52"	5	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Dual	4	N/A
Brentford	137	52"	5	ABS	13°	Silicon Steel 153mm x 17mm	Yes	Triple	3	20°
Carolina LED	129	52"	5	MDF	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	N/A
Casanova	134	52"	5	MDF	11°	Cold Rolled Steel 153mm x 15mm	Yes	Triple	3	N/A
Casanova Supreme	134	42"	4	MDF	12°	Cold Rolled Steel 153mm x 10mm	Yes	Dual	3	N/A
Cassidy	129	36"	5	MDF	12°	Silicon Steel 153mm x 12mm	Yes	Dual	3	18°
Castle	106	52"	5	Plywood	12°	Cold Rolled Steel 153mm x 15mm	Yes	Triple	3	18°
Castle LED	106	52"	5	Plywood	12°	Cold Rolled Steel 153mm x 15mm	Yes	Triple	3	18°
Cayuga	104	60"	6	Plywood	11°	Silicon Steel 188mm x 22mm	Yes	Dual	3	N/A
Comet (Outdoor)	139	52"	5	ABS	10°	Cold Rolled Steel 153mm x 18mm	Yes	Triple	3	18°
Comet	107	52"	5	Plywood	11°	Cold Rolled Steel 153mm x 15mm	Yes	Triple	3	18°
Contempra IV	130-131	52"	5	MDF	11°	Cold Rolled Steel 153mm x 15mm	Yes	Triple	3	N/A
Contempra Trio	132-133	42"	5	MDF	12°	Cold Rolled Steel 153mm x 10mm	Yes	Dual	3	N/A
Contractor's Choice	142	52"	5	MDF	12°	Silicon Steel 153mm x 15mm	Yes	Triple	3	11°
Cumulus	114	48"	3	MDF	12°	Silicon Steel 153mm x 15mm	Yes	Triple	3	N/A
Delancey	110	52"	3	ABS	13°	DC Motor 125S	Yes	N/A	6	18°
Delancey LED	110	52"	3	ABS	13°	DC Motor 125S	Yes	N/A	6	18°
Desoto	105	52"	4	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	18°
Elite	116	48"	3	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	18°
Fairview	125	52"	5	MDF	11°	Cold Rolled Steel 153mm x 12mm	Yes	Dual	3	N/A
Goodwin	128	52"	5	Plywood	13.5°	Silicon Steel 172mm x 17mm	Yes	Triple	3	21°
Great Falls	137	52"	4	ABS	12°	Silicon Steel 153mm x 15mm	Yes	Triple	3	18°
Hadley	132	42"	4	MDF	12°	Silicon Steel 153mm x 10mm	Yes	Triple	3	N/A
Harmony	113	48"	2	Plywood	13°	Silicon Steel 153mm x 20mm	Yes	Triple	4	20°
Industrial	141-142	56"	3	Steel	8°	Cold Rolled Steel 172mm x 12mm	No	Single	5	24°
Industrial (78003)	141	56"	3	Steel	8°	Cold Rolled Steel 171mm x 12mm	Yes	Single	4	24°
Industrial (78409)	142	56"	3	Steel	8°	Cold Rolled Steel 172mm x 12mm	No	Single	5	N/A
Lafayette	138	52"	5	ABS	12°	Silicon Steel 153mm x 15mm	Yes	Triple	3	11°
Lafayette LED	138	52"	5	ABS	12°	Silicon Steel 153mm x 15mm	Yes	Triple	3	11°
Lavada	114	48"	3	Plywood	12°	Silicon Steel 153mm x 15mm	Yes	Triple	3	20°
Newtown	128	42"	5	MDF	12°	Cold Rolled Steel 153mm x 10mm	Yes	Dual	3	18°
Oasis	139	48"	5	ABS	13°	Silicon Steel 153mm x 15mm	Yes	Triple	3	11°
Origami	121	24"	6	MDF	18°	Silicon Steel 153mm x 9mm	Yes	Dual	3	18°
Panorama	117	52"	5	MDF	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	15°
Petite	135	30"	6	MDF	18°	Cold Rolled Steel 153mm x 9mm	Yes	Dual	3	N/A
Quince	121	24"	6	MDF	18°	Silicon Steel 153mm x 9mm	Yes	Dual	3	18°
Richboro SE	128	42"	5	MDF	12°	Silicon Steel 153mm x 10mm	Yes	Dual	3	15°
Roundabout	118	30"	5	MDF	18°	Silicon Steel 153mm x 10mm	Yes	Dual	3	18°
Solana	113	48"	2	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	30°
Sparta	113	52"	2	Plywood	13°	Silicon Steel 153mm x 17mm	Yes	Triple	3	20°
Sumter LED	130	52"	5	MDF	12°	Cold Rolled Steel 153mm x 15mm	Yes	Triple	3	N/A
Swirl	126	52"	5	MDF	11°	Cold Rolled Steel 153mm x 15mm	Yes	Triple	3	18°
Techno	103	52"	3	ABS	13°	Silicon Steel 153mm x 17mm	Yes	Triple	4	20°
Techno II	103	72°	3	ABS	12°	DC165M	Yes	N/A	6	18°
Thurlow	123	54°	3	Plywood	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	18°
Troy	110	52"	3	Plywood	13°	Silicon Steel 153mm x 20mm	Yes	Triple	3	18°
Tulsa	124	52"	5	MDF	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	20°
Tulsa LED	124	52"	5	MDF	12°	Silicon Steel 153mm x 17mm	Yes	Triple	3	20°
Turbo Swirl	119	30"	6	MDF	18°	Silicon Steel 153mm x 10mm	Yes	Dual	3	18°
Turbo Swirl CFL	118	30"	6	MDF	18°	Cold Rolled Steel 153mm x 12mm	Yes	Dual	3	18°
Turbo Swirl LED	118	30"	6	MDF	18°	Cold Rolled Steel 153mm x 12mm	Yes	Dual	3	18°
Urban Gale	141	52"	3	ABS	9°	Cold Rolled Steel 171mm x 12mm	Yes	Dual	3	N/A
Vector Elite	116	42"	3	Plywood	16°	Silicon Steel 153mm x 10mm	Yes	Triple	3	19°
Vintage	127	52"	5	MDF	11°	Cold Rolled Steel 153mm x 15mm	Yes	Triple	3	18°
Vintage II	126	52"	5	MDF	11°	Cold Rolled Steel 153mm x 12mm	Yes	Triple	3	18°
Wengue	120	30"	3	MDF	18°	Silicon Steel 153mm x 9mm	Yes	Dual	3	18°
Xavier	117	44"	5	MDF	13°	Silicon Steel 153mm x 15mm	Yes	Triple	3	17°
Xavier II	117	52"	5	MDF	13°	Silicon Steel 153mm x 15mm	Yes	Triple	3	17°
Zander	107	52"	5	MDF	12°	Silicon Steel 153mm x 17mm	Yes	Single	3	20°
Zephyr	105	56"	5	Plywood	12°	Silicon Steel 172mm x 20mm	Yes	Dual	4	N/A

LED Technology Fan



# CEILING FAN SPECIFICATIONS

Family Name	Page #	Mount Type	Lead Wire Length	Remote Control	Extra Switch Housing Cap	Airflow CFM (High)	Watt (High)	CFM Watt (High)	RPM (High)	Amp (High)
Aerialist	112	Hugger	12"	Included	No	5661	33	172	211	0.45
Aiden	123	Combo	54"	Adaptable	No	3585	54	66	172	0.45
Alloy 42"	109	Down Rod Only	78"	Adaptable	No	2897	53	55	214	0.44
Alloy 52"	109	Down Rod Only	54"	Adaptable	No	3476	61	59	170	0.51
Alloy II	108	Down Rod Only	54"	Adaptable	No	4584	60	76	163	0.50
Alloy LED	108	Down Rod Only	54"	Adaptable	No	3576	61	59	170	0.51
Alta Vista	106	Down Rod Only	54"	Included	No	4789	59	81	175	0.52
Anderson	125	Down Rod Only	54"	Not Adaptable	Yes	4852	58	84	189	0.48
Arcadia	115	Combo	78"	Included	No	1877	50	37	222	0.42
Bendan	111	Down Rod Only	78"	Included	No	4478	58	77	173	0.49
Bendan LED	111	Down Rod Only	54"	Included	No	4452	62	72	178	0.53
Bocca	111	Combo	54"	Included	No	5193	64	81	186	0.56
Bolton	105	Down Rod Only	54"	Included	No	4625	60	77	158	0.52
Brentford	137	Down Rod Only	54"	Adaptable	No	4522	56	81	151	0.47
Carolina LED	129	Hugger	12"	Not Adaptable	Yes	3361	52	65	157	0.44
Casanova	134	Hugger	12"	Not Adaptable	No	3427	59	58	165	0.49
Casanova Supreme	134	Hugger	12"	Not Adaptable	Yes	1316	49	27	-	0.41
Cassidy	129	Combo	24"	Adaptable	No	2353	43	55	242	0.37
Castle	106	Combo	78"	Adaptable	No	3914	56	70	147	0.46
Castle LED	106	Combo	54"	Adaptable	No	3914	56	70	147	0.46
Cayuga	104	Down Rod Only	54"	Included	No	6098	81	75	145	0.68
Comet (Outdoor)	139	Combo	54"	Adaptable	No	4075	61	67	176	0.51
Comet	107	Combo	78"	Adaptable	No	3589	63	57	147	0.53
Contempra IV	130-131	Hugger	12"	Not Adaptable	No	3341	59	57	154	0.49
Contempra Trio	132-133	Hugger	12"	Not Adaptable	Yes	2829	56	51	220	0.47
Contractor's Choice	142	Combo	78"	Adaptable	No	4099	65	63	175	0.54
Cumulus	114	Down Rod Only	78"	Included	No	4858	53	92	204	0.44
Delancey	110	Down Rod Only	78"	Included	No	5206	32	163	173	0.47
Delancey LED	110	Down Rod Only	78"	Included	No	5206	32	163	173	0.47
Desoto	105	Down Rod Only	54"	Adaptable	No	4861	60	81	189	0.50
Elite	116	Combo	78"	Adaptable	No	3723	59	63	230	0.51
Fairview	125	Combo	24"	Included	No	3875	57	68	144	0.53
Goodwin	128	Down Rod Only	54"	Adaptable	No	5015	59	84	163	0.50
Great Falls	137	Combo	54"	Adaptable	No	4070	55	74	165	0.46
Hadley	132	Hugger	12"	Not Adaptable	Yes	2788	50	56	250	0.42
Harmony	113	Down Rod Only	78"	Adaptable	No	4611	56	82	190	0.46
Industrial	141-142	Down Rod Only	54"	Wall Control	No	5973	62	97	265	0.52
Industrial (78003)	141	Down Rod Only	54"	Wall Control	No	6045	64	94	276	0.54
Industrial (78409)	142	Down Rod Only	54"	Wall Control	No	5973	62	96	265	0.52
Lafayette	138	Combo	54"	Adaptable	Yes	4588	59	77	172	0.50
Lafayette LED	138	Combo	54"	Adaptable	Yes	4588	59	78	172	0.50
Lavada	114	Down Rod Only	78"	Adaptable	No	4757	52	91	204	0.44
Newtown	128	Combo	78"	Adaptable	No	3361	57	59	218	0.48
Oasis	139	Combo	54"	Adaptable	Yes	3983	50	80	146	0.42
Origami	121	Down Rod Only	78"	Adaptable	No	1174	29	40	310	0.26
Panorama	117	Combo	54"	Adaptable	No	1191	62	19	163	0.52
Petite	135	Hugger	12"	Not Adaptable	No	2027	46	44	275	0.39
Quince	121	Down Rod Only	78"	Adaptable	No	1270	28	45	323	0.25
Richboro SE	128	Combo	78"	Adaptable	No	3112	48	65	208	0.40
Roundabout	118	Down Rod Only	78"	Adaptable	No	2083	43	48	258	0.36
Solana	113	Down Rod Only	78"	Included	No	4698	50	94	246	0.42
Sparta	113	Down Rod Only	54"	Included	No	4292	53	81	198	0.45
Sumter LED	130	Hugger	12"	Not Adaptable	No	354	58	6	-	0.48
Swirl	126	Combo	78"	Adaptable	No	4259	66	65	185	0.55
Techno	103	Down Rod Only	78"	Included	No	4187	53	79	224	0.47
Techno II	103	Down Rod Only	54"	Included	No	7234	31	233	141	0.43
Thurlow	123	Down Rod Only	54"	Adaptable	No	5045	61	83	166	0.50
Troy	110	Down Rod Only	54"	Included	No	5301	59	89	200	0.49
Tulsa	124	Combo	54"	Not Adaptable	Yes	3315	58	57	168	0.49
Tulsa LED	124	Combo	54"	Not Adaptable	Yes	3315	59	57	168	0.49
Turbo Swirl	119	Combo	78"	Adaptable	No	369	54	7	233	0.45
Turbo Swirl CFL	118	Combo	78"	Adaptable	No	2564	54	47	233	0.45
Turbo Swirl LED	118	Combo	24"	Adaptable	No	2564	54	47	233	0.45
Urban Gale	141	Down Rod Only	54"	Included	No	5734	66	87	250	0.56
Vector Elite	116	Combo	78"	Adaptable	No	552	53	10	208	0.44
Vintage	127	Combo	78"	Adaptable	No	3835	64	60	166	0.54
Vintage II	126	Combo	78"	Adaptable	Yes	3787	61	62	169	0.51
Wengue	120	Down Rod Only	78"	Adaptable	No	1816	34	53	246	0.30
Xavier	117	Combo	78"	Adaptable	Yes	4281	64	67	229	0.53
Xavier II	117	Combo	78"	Adaptable	Yes	4476	65	69	150	0.54
Zander	107	Down Rod Only	54"	Included	Yes	4580	59	78	170	0.50
Zephyr	105	Down Rod Only	54"	Included	No	5450	69	79	159	0.58

LED Technology Fan



Visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for FTC energy guide information.



## CEILING FAN ACCESSORIES

Complement your Westinghouse ceiling fans with decorative pull chains and energy-saving light kits, while enjoying the convenience of our fan remote controls.

# LED CEILING FAN LIGHT KITS

**New!**


Designed to work with standard 42" to 52" ceiling fans with a center hole in the housing cap.



**77846**  
LED Schoolhouse  
Ceiling Fan Light Kit  
Oil Rubbed Bronze Finish with White Opal Glass  
Diameter: 8.25" Height: 6.75"  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp



**77853**  
LED Schoolhouse  
Ceiling Fan Light Kit  
White Finish with White Opal Glass  
Diameter: 8.25" Height: 6.75"  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp



Schoolhouse light kits include  
(1) Medium (E26) Base, 9 Watt  
ENERGY STAR® Omni A19 LED Lamp



**77851**  
LED Schoolhouse  
Ceiling Fan Light Kit  
Antique Brass Finish with White Opal Glass  
Diameter: 8.25" Height: 6.75"  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp



**77844**  
LED Schoolhouse  
Ceiling Fan Light Kit  
Polished Brass Finish with White Opal Glass  
Diameter: 8.25" Height: 6.75"  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp



**77852**  
3-in-1 LED Schoolhouse  
Ceiling Fan Light Kit  
with White Opal Glass  
Diameter: 8.25" Height: 6.75"  
Includes (1) Medium (E26) Base,  
9 Watt Omni A19 LED Lamp  
Includes (3) Optional 4" Fitters:  
• 1 White Finish Fitter  
• 1 Oil Rubbed Bronze Finish Fitter  
• 1 Brushed Nickel Finish Fitter



Schoolhouse Light Kits are approved for damp location.



**77845**  
LED Cluster Ceiling Fan Light Kit  
Polished Brass Finish with  
Frosted Ribbed Glass  
Diameter: 12.75" Height: 7"  
Includes (3) Medium (E26) Base,  
5 Watt Omni A15 LED Lamps



**77849**  
LED Cluster Ceiling Fan Light Kit  
Brushed Nickel Finish with  
Frosted Ribbed Glass  
Diameter: 12.75" Height: 7"  
Includes (3) Medium (E26) Base,  
5 Watt Omni A15 LED Lamps



Three Light Cluster light kits include  
(3) Medium (E26) Base, 5 Watt  
Omni A15 LED Lamps



**77850**  
LED Cluster Ceiling Fan Light Kit  
Oil Rubbed Bronze Finish with  
Frosted Ribbed Glass  
Diameter: 12.75" Height: 7"  
Includes (3) Medium (E26) Base,  
5 Watt Omni A15 LED Lamps



**77848**  
LED Cluster Ceiling Fan Light Kit  
Antique Brass Finish with  
Frosted Ribbed Glass  
Diameter: 12.75" Height: 7"  
Includes (3) Medium (E26) Base,  
5 Watt Omni A15 LED Lamps



**77847**  
LED Cluster Ceiling Fan Light Kit  
White Finish with  
Frosted Ribbed Glass  
Diameter: 12.75" Height: 7"  
Includes (3) Medium (E26) Base,  
5 Watt Omni A15 LED Lamps

All ceiling fan light kits are CUL listed.

# CATHEDRAL CEILING FAN CANOPY KITS



## CATHEDRAL CEILING FAN CANOPY KITS INCLUDE:

- Decorative Canopy
- Retaining Ball
- Universal Mounting Plate
- Mounting Bracket
- Decorative Hole Cover Ring
- Mounting Hardware
- 1/2" Down Rod Sleeve Adapter
- Complete Installation Instructions

The only cathedral ceiling fan canopy kit that is remote control adaptable up to a 45° angle for 1/2" or 3/4" I.D. down rods. No visible screws. Decorative hole cover ring included for a clean finished look.

Unique patent-pending design makes it easy to install a remote control receiver, even up to a 45° angle.

*Cathedral Ceiling Fan Canopy Kits can be mounted onto a cathedral ceiling having up to a 45° angle.*


*For Use With 1/2" or 3/4" I.D. Down Rods  
85 lb. Load Rating*



**70031**  
Brushed Nickel Finish



**70032**  
Oil Rubbed Bronze Finish




# EXTENSION DOWN RODS



White



Antique Brass



Brushed Nickel



Oil Brushed Bronze

For optimum performance, ceiling fan blades should be at least 7' from the floor but no higher than 8-9' in order to best cool a room.

For ceilings 9' and higher, an extension down rod is recommended to bring the ceiling fan down to the proper height above the floor.



## 1/2" EXTENSION DOWN RODS

Finish	12"	24"	36"
Antique Brass	77241	77244	N/A
Brushed Nickel	77491	77492	N/A
White	77240	77243	77246

1/2" is the nominal dimension of these down rods.

## 3/4" EXTENSION DOWN RODS

Finish	12"	18"	24"	36"
Oil Brushed Bronze	77258	N/A	77259	N/A
Antique Brass	77249	N/A	77252	N/A
Brushed Nickel	77526	N/A	77527	77528
White	77251	77265	77254	77257

3/4" is the nominal dimension of these down rods.



# CEILING FAN CONTROLS



- 77872**  
Single Slide Ceiling Fan Wall Control
- Turn any 3 speed fan into a 4 speed fan
  - High/Medium-High/Medium/Low fan speeds
  - Easy 2 wire installation in standard junction box
  - Matching wall plate included

Max. Fan Amp 1.25



- 77870**  
Ceiling Fan and Light Remote Control
- High/Medium/Low fan speeds and Off button
  - Full range light dimmer
  - Operates up to a distance of 40 feet
  - Universal receiver fits most ceiling fans
  - Installs quickly, even in pre-mounted fans
  - Wall Bracket included
  - (1) 9 Volt battery included

Max. Fan Amp 1.25  
Max. Light 300 Watt



- 77873**  
Dual Slide Ceiling Fan/Light Wall Control
- Turn any 3 speed fan into a 4 speed fan
  - High/Medium-High/Medium/Low fan speeds
  - Full range sliding light dimmer
  - Easy 3 wire installation in standard junction box
  - Replaces toggle switch
  - Matching wall plate included

Max. Fan Amp 1.25  
Max. Light 300 Watt



- 77874**  
Thermostat Ceiling Fan/Light Remote Control
- Automatic On/Off and Speed Control based on room temperature
  - ½ - 24 hour programmable fan/light shut off timers
  - 3-Minute Auto Light Shut Off
  - High/Medium/Low fan speeds and Off button
  - Full range light dimmer
  - Operates up to a distance of 40 feet
  - Universal receiver fits most ceiling fans
  - Installs quickly, even in pre-mounted fans
  - (4) AAA batteries included

Max. Fan Amp 1.25  
Max. Light 300 Watt



- 77875**  
Ceiling Fan and Light Wall Control
- High/Medium/Low fan speeds and Off button
  - Full range light dimmer
  - Wireless communication between transmitter and receiver
  - Operates up to a distance of 40 feet
  - Easy 2 wire installation in standard junction box
  - Universal receiver fits most ceiling fans
  - Matching wall plate included

Max. Fan Amp 1.25  
Max. Light 300 Watt



- 77871**  
Ceiling Fan and Light Remote Control
- High/ Medium/ Low fan speeds and Off button
  - Full range light dimmer
  - Operates up to a distance of 40 feet
  - Million code pairings for the frequency code setting
  - Dip switch provides the option of full dimming functionality when used with dimmable lamps. This function can be disabled when using non-dimmable lamps
  - Universal receiver fits most ceiling fans
  - Installs quickly, even in pre-mounted fans
  - Wall Bracket included
  - (2) AAA batteries included

Max. Fan Amp 0.8  
Max. Light 300 Watt



All fan controls are for SINGLE FAN USAGE ONLY.  
All fan controls are for INDOOR USE ONLY.

# PULL CHAINS

Easily add personality to your ceiling fan.



**New!**

**77135**  
Fan and Bulb  
Brushed Nickel  
Finish



**New!**

**77126**  
Clear and Blue  
Drizzle Glass  
Brushed Nickel Finish



**New!**

**77129**  
Clear Flame  
Glass  
Oil Rubbed  
Bronze Finish



**New!**

**77132**  
Clear and  
Frost Glass  
Brushed Nickel  
Finish



**77642**  
Orange and  
Green Daisy Beads  
Polished  
Brass Finish



**77125**  
Amber  
Alabaster Glass  
Oil Rubbed  
Bronze Finish



**77620**  
White Swirl and  
Multi-Color Dotted  
Glass Orb  
Brushed  
Nickel Finish



**77621**  
Clear and  
Blue Swirl  
Glass Orb  
Brushed  
Nickel Finish



**77118**  
Clear and  
Amber Swirls  
Glass Orb  
Oil Rubbed Bronze  
Finish



**77640**  
Cobalt  
Twist Glass  
Brushed  
Nickel Finish



**77122**  
Yellow  
Spiral Glass  
Oil Rubbed  
Bronze Finish



**77215**  
Trophy  
Brushed  
Nickel Finish



**77108**  
Trophy  
Antique  
Brass Finish



**77214**  
Trophy  
Oil Rubbed  
Bronze Finish



**77103**  
Pendant  
Brushed  
Nickel Finish

All pull chains include a 12" beaded chain unless otherwise noted.

CARDED PRODUCT SOLD IN INNER PACK ONLY.



**77029**  
Light Bulb  
Brushed  
Nickel Finish



**77030**  
Light Bulb  
Oil Rubbed  
Bronze Finish



**77220**  
Light Bulb  
Antique  
Brass Finish



**77036**  
Fan  
Brushed  
Nickel Finish



**77083**  
Fan  
Oil Rubbed  
Bronze Finish



**77225**  
Fan  
White  
Chrome Finish



**77224**  
Fan  
Antique  
Brass Finish



**77087**  
Natural Finish  
Wooden Handle  
Polished  
Brass Finish



**77291**  
Walnut  
Wooden Cone  
Antique  
Brass Finish



**77009**  
White  
Wooden Cone  
Polished  
Brass Finish



**77292**  
White  
Wooden Cone  
Chrome  
Finish



**77019**  
Natural Finish  
Wooden Cone  
Polished  
Brass Finish



**77008**  
Walnut  
Wooden Cone  
Polished  
Brass Finish



**77014**  
White  
Wooden Knob  
Polished  
Brass Finish



**77013**  
Walnut  
Wooden Knob  
Polished  
Brass Finish



**70661 - 36" Chain**  
**77069 - 12" Chain**  
Walnut  
Wooden Ball  
Polished  
Brass Finish



**77290**  
Walnut  
Wooden Ball  
36" Antique  
Brass Finish



**77072**  
White  
Wooden Ball  
Polished  
Brass Finish



**77007**  
Sculptured  
Walnut  
Wooden Ball  
Polished  
Brass Finish

All pull chains include a 12" beaded chain unless otherwise noted.

CARDER PRODUCT SOLD IN INNER PACK ONLY.

# PULL CHAINS



**77104**  
Beaded Ball  
Brushed  
Nickel Finish



**77096**  
Beaded Ball  
Oil Rubbed  
Bronze Finish



**77217**  
Ball  
Brushed  
Nickel Finish



**77218**  
Ball  
Old Chicago Finish



**77004**  
Ball  
Solid Brass



**77005**  
Teardrop  
Polished  
Brass Finish



**77121**  
Chrome Finish  
and Ceramic  
Black Accent



**77095**  
Polished  
Brass Finish  
and Ceramic  
White Accent



**77293**  
Baseball  
Chrome Finish



**77134**  
Acrylic Dolphin  
Polished Brass Finish



**77006**  
Acrylic Cylinder  
Polished Brass Finish



**77088**  
Acrylic Teardrop  
Polished Brass Finish



**77084**  
Acrylic Sphere  
Polished Brass Finish



**77093**  
Acrylic Diamond  
Polished Brass Finish



**77289**  
Acrylic Diamond  
Chrome Finish

All pull chains include a 12" beaded chain unless otherwise noted.

# ALL PURPOSE DUSTERS



**77000**  
Chenille Microfiber  
Adjustable Brush Duster  
with Telescopic Pole

- Extends to 62" and adjusts to any angle.
- Telescopic handle and adjustable head for cleaning hard-to-reach items.
- Attracts and holds dust.
- Cleans without using sprays or chemicals.
- Hand washable.



**77105**  
All Purpose  
Electrostatic Duster

- Telescopic handle extends up to 72".
- Flexible head adjusts to any angle.
- Perfect for cleaning fan blades, fixtures or any other hard-to-reach household items.

CARDED PRODUCT SOLD IN INNER PACK ONLY.




# REPLACEMENT FAN BLADE ARMS

5 Piece Set - Installation Hardware Included



- 77400 - 42" Polished Brass Finish
- 77401 - 42" White Finish
- 77402 - 42" Antique Brass Finish
- 77403 - 42" Brushed Nickel Finish
- 77408 - 42" Oil Rubbed Bronze Finish

- 77405 - 52" Polished Brass Finish
- 77406 - 52" White Finish
- 77407 - 52" Antique Brass Finish
- 77409 - 52" Brushed Nickel Finish
- 77417 - 52" Oil Rubbed Bronze Finish



### FAN BLADE HOLE DIMENSIONS

Dimension	52" Parts	42" Parts
A	31 <sup>5</sup> / <sub>16</sub> "	3 <sup>1</sup> / <sub>2</sub> "
B	2 <sup>3</sup> / <sub>4</sub> "	2 <sup>5</sup> / <sub>8</sub> "
C	2 <sup>1</sup> / <sub>16</sub> "	1 <sup>1</sup> / <sub>2</sub> "

# FAN REPLACEMENT BLADES & CANOPY KITS

42" Replacement Blades - Length: 16.5" Width: 5"  
 52" Replacement Blades - Length: 20.5" Width: 5.38"



77414 - 52" White  
 Outdoor ABS Fan Blades  
 5 Blade Set



77411 - 42" White/Bleached Oak  
 77416 - 52" White/Bleached Oak  
 Reversible MDF Fan Blades  
 5 Blade Set



77060 - Antique Brass Finish  
 77061 - Polished Brass Finish  
 77268 - White Finish  
 Canopy Kit  
 1/2" I.D. Ball Included  
 Can be mounted onto a cathedral ceiling having up to a 25° angle  
 100 lb. Load Rating



77410 - 42" Oak/Walnut  
 77415 - 52" Oak/Walnut  
 Reversible MDF Fan Blades  
 5 Blade Set



77413 - 52" Dark Brown Finish  
 Outdoor ABS Replacement  
 Fan Blades  
 5 Blade Set



77079 - White Finish  
 Canopy Kit  
 3/4" I.D. Ball Included  
 Can be mounted onto a cathedral ceiling having up to a 25° angle  
 100 lb. Load Rating

CARDED PRODUCT SOLD IN INNER PACK ONLY.

# BEADED CHAINS, CONNECTORS & HARDWARE



**77044 - Solid Brass**  
Six Beaded  
Chain Connectors



**77046 - White**  
Six Beaded  
Chain Connectors



**77045 - Chrome**  
Six Beaded  
Chain Connectors



**77066 - Antique Brass**  
Six Beaded  
Chain Connectors




**\*16572 - Brass**  
Beaded  
Chain Connector


**Beaded Chain with Connector**

.011 Gauge 1/8" Diameter Ball 75 Balls per Foot


Item No.	Length	Finish
70168	5 Ft.	Brass
77012	1 Ft.	Solid Brass
77050	3 Ft.	Solid Brass
77043	12 Ft.	Solid Brass
77064	3 Ft.	Antique Brass
77109	12 Ft.	Antique Brass
77051	3 Ft.	White Plastic
77054	3 Ft.	Oil Rubbed Bronze
77049	3 Ft.	Stainless Steel
77238	3 Ft.	Brushed Nickel
77063	3 Ft.	Chrome
77107	12 Ft.	Chrome




70168




77012  
77050  
77043




77238




77049




77063  
77107



77051



77054



77064  
77109



**\*16576 - Brass Finish**  
End Bell  
For Beaded Chain  
or Pull Cord



**\* 22370**  
77077  
Porcelain  
Fixture Socket  
10" Wire Leads  
Medium Base, 1/8-IP Hickey  
18 Gauge, 105° Leads  
660 Watts Max., 250 Volts  
Height - 2.41"



**Beaded Chain**

.011 Gauge 1/8" Diameter Ball 75 Balls per Foot


Item No.	Length	Finish
* 16565	Sold by Foot or 250' Spool	Nickel
* 16564	Sold by Foot or 250' Spool	Brass



**77047 - Polished Brass**  
**77048 - Antique Brass**  
10 Piece Motor Screw Kit  
For Mounting Fan Blade Arm  
to Motor Housing




**77040 - Polished Brass**  
**77041 - Antique Brass**  
12 Fitter Screws  
For Fan Lights



**77015**  
Fan Blade  
Balancing Kit  
Includes:  
2-5 Gram Self-Adhering Weights  
• 1 Balancing Clip



**77059**  
Canopy Bracket  
Black Finish  
Designed For Use With 1/2" or  
3/4" I.D. Down Rods and Canopy  
Ball (sold separately)  
Mounting Hardware Included



**77058**  
For 1/2" I.D. Down Rods  
**77269**  
For 3/4" I.D. Down Rods  
Black Canopy Ball  
For Use With 1/2" or 3/4" I.D. Down  
Rods and Bracket #77059  
Mounting Hardware Included



**77016**  
20 - 1/2" Knurled Head Screws  
Assorted for Fan Lights and Fan Blades  
Includes:  
• 5 - 8-32 Antique Brass  
• 5 - 8-32 Polished Brass  
• 5 - 10-24 Antique Brass  
• 5 - 10-24 Polished Brass

# FAN SWITCHES



**77022**  
Fan  
Light Switch  
Chrome Pull Chain,  
2 Wire, Single Pole Switch  
3' Braided Cord  
3A, 250 VAC  
6A, 125 VAC



**77023**  
Fan  
Light Switch  
Polished Brass Pull Chain,  
2 Wire, Single Pole Switch  
2' Braided Cord  
3A, 250 VAC  
6A, 125 VAC



**77287**  
Fan  
Light Switch  
Antique Brass Pull Chain,  
2 Wire, Single Pole Switch  
3' Braided Cord  
3A, 250 VAC  
6A, 125 VAC



**77288 - Dual Capacitor,  
4-Wire Unit**  
3-Speed Fan Switch  
With Antique Brass  
Pull Chain, 2' Braided Cord  
3A, 250 VAC  
6A, 125 VAC



**77286 - Single Capacitor,  
4-Wire Unit**  
3-Speed Fan Switch  
With Antique Brass  
Pull Chain, 2' Braided Cord  
3A, 250 VAC  
6A, 125 VAC



**77075 - with Polished Brass  
Pull Chain**  
**77073 - with Antique Brass  
Pull Chain**  
3-Speed Fan Switch  
Triple Capacitor  
8-Wire Unit  
2' Braided Cord  
3A, 250 VAC  
6A, 125 VAC



**77021 - Single Capacitor,  
4-Wire Unit**  
3-Speed Fan Switch  
With Polished Brass  
Pull Chain, 2' Braided Cord  
3A, 250 VAC  
6A, 125 VAC




**77270**  
48" Down Rod Wire  
Extension Kit  
4 Wires with  
4 Connectors



**77285 - 3-Wire Unit**  
3-Way Fan  
Light Switch  
With Antique Brass  
Pull Chain, 2' Braided Cord  
3A, 250 VAC  
6A, 125 VAC



**77052 - 3-Wire Unit**  
3-Way Fan  
Light Switch  
With Polished Brass  
Pull Chain, 2' Braided Cord  
3A, 250 VAC  
6A, 125 VAC




**77091**  
Fan Capacitor  
3 MFD and 6.5 MFD  
3-Wire 150V

CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack





## CEILING FAN & LIGHT FIXTURE ACCESSORIES

From ornamental ceiling medallions to secure support braces and boxes, Westinghouse offers a full line of both decorative and functional accessories to enhance and complete any ceiling fan or light fixture installation.



# Recessed Light Converter

Transform existing recessed lighting into a pendant or other light fixture!




## 01011

### Recessed Light Converter

- Quick and easy home upgrade with no remodeling.
- Unique patent pending design.
- Adjust to any recessed can size between 4" - 6" diameter.
- No visible screws or hardware.
- Perfect for hanging a pendant or other lighting fixtures.
- Decorative 6" diameter medallion can be painted to match any décor.
- Works with existing recessed cans that use medium base lamps.\*
- 50 lb. maximum load rating.

*Note: Paintable decorative medallion and metal plate are optional when used on a 4" diameter recessed can.*





## 0101108

### Recessed Light Converter Shelf Display

11.3" L x 9.3" W x 10.3" H

- Easily change ordinary recessed lights into beautiful, modern lighting.
- Display the Recessed Light Converter using our Shelf Merchandiser.
- The perfect way to display inventory and increase your sales.
- Each display comes with 6 pieces of the Recessed Light Converter.



PATENTED  
TECHNOLOGY

US PATENT NO.  
9,496,699

\*Recessed Light Converter works with existing recessed cans that use medium base PAR16, R16, A19, R20, PAR20, BR25, BR30, R30, PAR30, BR38, PAR38, BR40 or R40 lamps.

# EASY-TO-INSTALL ELEGANCE



## CHOOSING A MEDALLION

Consider these four factors when selecting the appropriate ceiling medallion.

### FAN OR FIXTURE SIZE

- Medallions should be smaller or larger than the diameter of your ceiling fan or lighting fixture. They should not be the same size.

### CEILING HEIGHT

- Higher ceilings can accommodate larger medallions.
- 28" or larger medallions complement a two-story foyer.

### ROOM SIZE

- Large rooms accommodate large medallions.
- For a typical dining room with an 8' to 9' ceiling, an 18" to 26" diameter medallion works well.

### MATERIAL

- Polyurethane medallions resemble traditional plaster medallions.
- Molded plastic medallions are lightweight and can be simply installed with adhesive.



## PERSONALIZE YOUR DECORATIVE POLYURETHANE MEDALLION

- Lightweight polyurethane medallions can be installed finished or unfinished.
- Available in well-known architectural styles to complement molding or other architectural details.
- Installation hardware is included in all Westinghouse polyurethane ceiling medallions.
- For use with ceiling fans or lighting fixtures.
- Easily drilled or screwed.
- Will not warp, split or splinter.
- Easily caulked or spackled to hide installation hardware.



Simply apply adhesive and screw or nail into any surface.



Use unpainted or paint with any latex or oil based paint to create a look that matches any décor.

# POLYURETHANE MEDALLIONS

## INCLUDES MOUNTING HARDWARE:

- 1 - 3" 1/8-IP nipple
- 2 - 2" 8-32 crossbar screws
- 3 - 1 1/2" drywall screws



**77762**  
**Colonnade**  
White Finish  
Diameter: 12.38"  
Center Opening: 4"



**77750**  
**Bellezza**  
White Finish  
Diameter: 14.09"  
Center Opening: 4"



**77754**  
**Cape May**  
White Finish  
Diameter: 28"  
Center Opening: 4"



**77757**  
**Sofia**  
White Finish  
Diameter: 21"  
Center Opening: 4"



**77752**  
**Soleil**  
White Finish  
Diameter: 20"  
Center Opening: 4"



**77756**  
**Francesca**  
White Finish  
Diameter: 18"  
Center Opening: 4"



**77764**  
**Round Parisian Scroll**  
Antique Bronze Finish  
Diameter: 16"  
Center Opening: 4"

# MOLDED PLASTIC MEDALLIONS

Adhesive or additional mounting hardware required.



**77733**  
**Round Beaded**  
 White Finish  
 Diameter: 16"  
 Center Opening: 4"



**77732**  
**Smooth**  
 White Finish  
 Diameter: 16"  
 Center Opening: 4"



**77037**  
**Smooth**  
 White Finish  
 Diameter: 10"  
 Center Opening: 4"



**77027**  
**Victorian**  
 White Finish  
 Diameter: 10"  
 Center Opening: 4"



**77028**  
**Victorian**  
 White Finish  
 Diameter: 16"  
 Center Opening: 4"



**77035**  
**Textured**  
 White Finish  
 Diameter: 16"  
 Center Opening: 4"




**77034**  
**Split Design**  
 White Finish  
 Diameter: 16"  
 Center Opening: 4"



## IDEAL FOR RETROFIT APPLICATION NO ATTIC ACCESS REQUIRED

- Fits 16" to 24" ceiling joists.
- Patented design provides fast fingertip expansion and positive attachment to joists.
- Fits all ceiling fans.
- Position box anywhere along the brace.
- For fixture support of 150 lbs. or less on 16" centers.
- For fixture support of 50 lbs. or less on 24" centers.
- Acceptable for fan support of 70 lbs. or less.

Includes Mounting Hardware & Instructions



### Additional Security from Screw Connector

01010

Saf-T-Brace®

Box Depth 1½"

Heavy Duty, 15.5 Cubic Inch Dual Mount\* Electrical Box

6 Knockouts for Conduit or Romex

Individually Packaged, 24 Per Cut Case

**Extra Strong Grip**



Saf-T-Brace® Display (18"L x 6 1/8"D x 8"H)  
#01010DISP




For more display information, contact your Westinghouse Sales Representative.




### Step 1

Easy installation from below ceiling through any 4" diameter hole.




### Step 2

Install end "A" by turning unit clockwise and applying pressure toward the ceiling joist.




### Step 3

Slide unit toward other joist and again apply clockwise pressure.



### Step 4

Attach electrical box and install fan or lighting fixture per manufacturer's instructions.





\*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

# Saf-T-Brace®

## IDEAL FOR RETROFIT APPLICATION NO ATTIC ACCESS REQUIRED

- Fits 16" to 24" ceiling joists.
- Patented design provides fast fingertip expansion and positive attachment to joists.
- Fits all ceiling fans.
- Position box anywhere along the brace.
- Features convenient magnet that holds box to brace during installation.
- For fixture support of 150 lbs. or less on 16" centers.
- For fixture support of 50 lbs. or less on 24" centers.
- Acceptable for fan support of 70 lbs. or less.




### Teeth Twist and Lock into Joist to Create More Secure Connection

#### 01100 Saf-T-Brace®

Box Depth 1 1/2"  
Heavy Duty, 15.5 Cubic Inch Dual Mount\* Electrical Box  
6 Knockouts for Conduit or Romex  
Individually Packaged, 24 Per Cut Case  
Strong Grip


#### Step 1

Easy installation from below ceiling through any 4" diameter hole.




#### Step 2

Rotate bar until teeth are fully embedded into joist.



#### Step 3

Attach electrical box and install fan or lighting fixture per manufacturer's instructions.





\*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

# Saf-T-Brace®

## IDEAL FOR RETROFIT APPLICATION NO ATTIC ACCESS REQUIRED

- Fits 16" to 24" ceiling joists.
- Patented design provides fast fingertip expansion and positive attachment to joists.
- Fits all ceiling fans.
- Position box anywhere along the brace.
- Features convenient magnet that holds box to brace during installation.
- For fixture support of 150 lbs. or less on 16" centers.
- For fixture support of 50 lbs. or less on 24" centers.
- Acceptable for fan support of 70 lbs. or less.



**Includes Larger Box for Increased Wire Capacity**

**01400**


**Saf-T-Brace®**

**Box Depth 2 1/8"**

*Heavy Duty, 21.5 Cubic Inch Dual Mount\* Electrical Box  
6 Knockouts for Conduit or Romex  
Individually Packaged, 12 Per Cut Case  
Strong Grip*


### Step 1

Easy installation from below ceiling through any 4" diameter hole.




### Step 2

Rotate bar until teeth are fully embedded into joist.



### Step 3

Attach electrical box and install fan or lighting fixture per manufacturer's instructions.





\*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

# Saf-T-Bar®

## IDEAL FOR NEW CONSTRUCTION ATTIC ACCESS REQUIRED

- Fits 16" to 24" ceiling joists.
- Can be used with engineered truss.
- Fits all ceiling fans.
- Easy 4-step installation.
- Position box anywhere along the brace.
- For fixture support of 150 lbs. or less on 16" centers.
- For fixture support of 90 lbs. or less on 24" centers.
- Acceptable for fan support of 70 lbs. or less.

Includes Mounting Hardware & Instructions



Can be used with Engineered Truss

**01525 & 0152511**  
**Saf-T-Bar®**

Box Depth 1½"  
Heavy Duty, 15.5 Cubic Inch Dual Mount\* Electrical Box  
6 Knockouts for Conduit or Romex  
01525 Individually Packaged, 12 Per Cut Case  
0152511 Bulk Packed, 12 Per Cut Case

### ENGINEERED TRUSS APPLICATION



Saf-T-Bar® Display (18"L x 6 1/8"D x 8"H)  
#01525DISP



For more display information, contact your Westinghouse Sales Representative.




\*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.



# Saf-T-Box®

## HEAVY DUTY SUPPORT FOR NEW CONSTRUCTION OR FOR APPLICATIONS WHERE ATTIC IS ACCESSIBLE

- Includes mounting hardware and instructions.
- For fixture support of 150 lbs. or less.
- Acceptable for fan support of 70 lbs. or less.



### 01020 & 0102011

#### Saf-T-Box®

Fits All Ceiling Fans  
3 Knockouts for Conduit or Romex  
Box Depth 1½"

#### Heavy Duty

15.5 Cubic Inch Electrical Box  
01020 Individually Packaged, 24 Per Cut Case  
0102011 Bulk Packed, 48 Per Cut Case



### 01050 & 0105011

#### Saf-T-Box®

#### 3 Knockouts for Conduit or Romex

1 Romex Clamp  
Box Depth 1½"  
Heavy Duty, 15.5 Cubic Inch  
Dual Mount\* Electrical Box



### 010521

#### Saf-T-Box®

#### 6 Knockouts for Conduit or Romex

1 Romex Connector  
Box Depth 1½"  
Heavy Duty, 15.5 Cubic Inch  
Dual Mount\* Electrical Box



### 010401

#### Saf-T-Box®

3 Knockouts for Conduit or Romex  
1 Romex Clamp

#### Box Depth 2½"

Heavy Duty, 21.5 Cubic Inch  
Dual Mount\* Electrical Box



Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

# Sidemount Plus Fan Box®

## IDEAL FOR REMODEL APPLICATIONS

- Sidemount bracket is removable for easy replacement of existing nail-on boxes without attic access.
- Fits all ceiling fans.
- Includes mounting hardware and instructions.
- For fixture support of 70 lbs. or less.
- Acceptable for fan support of 70 lbs. or less.

Sidemount Plus Fan Box® Display (18"L x 6 1/8"D x 8"H)  
#01240DISP



For more display information, contact your Westinghouse Sales Representative.

### 01240 & 0124011

#### Sidemount Plus Fan Box®

3 Knockouts for Conduit or Romex


**Box Depth 2 1/8"**

Heavy Duty, 21.5 Cubic Inch

Dual Mount\* Electrical Box

01240 Individually Packaged, 4 Per Cut Case


0124011 Bulk Packed, 12 Per Cut Case



### Easy to Install through 4" Hole in Sheetrock


#### Step 1

Mount bracket to joist through 4" hole in sheetrock.



#### Step 2

Pull wire into box and remount box to bracket.



### 01250 & 0125011

#### Sidemount Plus Fan Box®

3 Knockouts for Conduit or Romex

**Box Depth 1 1/2"**

Heavy Duty, 15.5 Cubic Inch

Dual Mount\* Electrical Box

01250 Individually Packaged, 24 Per Cut Case

0125011 Bulk Packed, 24 Per Cut Case



\*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

## IDEAL FOR NEW CONSTRUCTION OR REMODEL APPLICATIONS

- Fits all ceiling fans.
- Includes mounting hardware and instructions.
- For fixture support of 150 lbs. or less.
- Acceptable for fan support of 70 lbs. or less.

### 01030 & 0103011

#### Saf-T-Pan®


2 Knockouts for Conduit or Romex

**Box Depth 5/8"**

Heavy Duty, 8 Cubic Inch Dual Mount\* Electrical Pan

01030 Individually Packaged, 24 Per Cut Case

0103011 Bulk Packed, 48 Per Cut Case



### 01036 & 0103611

#### Saf-T-Pan®

5 Knockouts for Conduit or Romex

**Box Depth 1/2"**

Heavy Duty, 6 Cubic Inch Dual Mount\* Electrical Pan

01036 Individually Packaged, 12 Per Cut Case

0103611 Bulk Packed, 24 Per Cut Case




\*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

# Fan Master Jr.<sup>®</sup> & Fan Master<sup>®</sup>

## IDEAL FOR NEW CONSTRUCTION APPLICATIONS

- Fits all ceiling fans.
- 2 knockouts for Conduit or Romex.
- Two hour fire rating.
- Includes mounting hardware and instructions.
- For fixture support of 150 lbs. or less.
- Acceptable for fan support of 70 lbs. or less.



**0252511**  
**Fan Master Jr.<sup>®</sup>**  
 Height 4"  
 Box Depth ½"  
**13.4 Cubic Inch Wiring Capacity**  
 0252511 Bulk Packed, 12 Per Cut Case

Application Illustration  
 for All Fan Master Products



(Shown with 0200011)  
 Built-in tabs allow for easier hands free installation

**Get the Wiring Space  
 You Need...  
 Where You Need It!**

Ceiling fan or lighting fixture attaches to structure support, not to plastic



Clips inside box hold screws during initial installation



**0200011**  
**Fan Master<sup>®</sup>**  
 Height 4 13/16"  
 Box Depth 5/8"  
**16.5 Cubic Inch Wiring Capacity**  
 0200011 Bulk Packed, 24 Per Cut Case

Fan Master Jr.<sup>®</sup> Display (18"L x 6 1/8"D x 8"H)  
**#02525DISP**



For more display information, contact your Westinghouse Sales Representative.



\*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.




# Saf-T-Grid®


## SAFELY INSTALLS FANS AND FIXTURES IN SUSPENDED CEILING APPLICATIONS

- Reduce ceiling vibration and provide safe secure installation.
- Fits 2' x 2' and 2' x 4' ceiling tile gridwork.
- Position box anywhere along the brace.
- Fits all ceiling fans.
- For fixture support of 50 lbs. or less.
- Acceptable for fan support of 50 lbs. or less.

Includes Mounting Hardware & Instructions



All weight is carried by building structure, not by gridwork



\*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.



# Westinghouse

INNOVATION YOU CAN BE SURE OF



## REPLACEMENT GLASSWARE & ASSORTED SHADES

Refreshing a light fixture or ceiling fan with our unique selection of shades is an easy design upgrade. From classic glass diffusers to vibrant art glass shades, Westinghouse offers something for all of your lighting needs.

# 2¼" FITTER SHADES

2¼" fitter glass is perfect for use with pendants, vanity fixtures and ceiling fans.



**New!**

- **85004**  
**White Linen**  
**Cube Shade**  
Fitter: 2.25"  
Height: 7"  
Width: 3.94"



- **85044**  
**Wavy White**  
**Glazed Cube Shade**  
Fitter: 2.25"  
Height: 6"  
Width: 3.75"



- **85045**  
**Rippled White Glazed**  
**Rectangular Shade**  
Fitter: 2.25"  
Height: 6"  
Width: 6"  
Depth: 4"



- 81000**  
**White Alabaster**  
**Flared Bell Shade**  
Fitter: 2.25"  
Height: 4.33"  
Diameter: 6.97"



- 81002**  
**Caramel Scavo**  
**Bell Shade**  
Fitter: 2.25"  
Height: 4.61"  
Diameter: 6.06"



- **85043**  
**White Opal**  
**Bell Shade**  
Fitter: 2.25"  
Height: 4.88"  
Diameter: 6.61"



- 85047**  
**Frosted**  
**Dome Shade**  
Fitter: 2.25"  
Height: 4.69"  
Diameter: 5.79"



- 81017**  
**Smoldering Scavo**  
**Cone Shade**  
Fitter: 2.25"  
Height: 5.60"  
Diameter: 4.75"



- **81006**  
**Lunar Weave**  
**Flared Cube Shade**  
Fitter: 2.25"  
Height: 5.27"  
Width: 5"



- **81013**  
**White Linen**  
**Flared Cube Shade**  
Fitter: 2.25"  
Height: 5.27"  
Width: 5"



- **81009**  
**Amber Linen**  
**Flared Cube Shade**  
Fitter: 2.25"  
Height: 5.27"  
Width: 5"



- **81014**  
**White Linen**  
**Cylinder Shade with**  
**Translucent Band**  
Fitter: 2.25"  
Height: 5.12"  
Diameter: 3.94"



- **81015**  
**Amber Harvest**  
**Cylinder Shade**  
Fitter: 2.25"  
Height: 5.12"  
Diameter: 3.94"



- **81016**  
**White Linen**  
**Cylinder Shade**  
Fitter: 2.25"  
Height: 5.12"  
Diameter: 3.94"



- **85006**  
**Ice**  
**Cylinder Shade**  
Fitter: 2.25"  
Height: 5.15"  
Diameter: 4"

•Hand Blown Glass

# RETRO SHADE ASSORTMENT



•81020  
**Champagne Glass  
 Rippled Cone Shade**  
 Fitter: 2.25"  
 Height: 7"  
 Diameter: 5"




•81021  
**Clear Glass  
 Open Teardrop Shade**  
 Fitter: 2.25"  
 Height: 7"  
 Diameter: 7.50"



 **Westinghouse**  
**VINTAGE LAMPS**

Add Westinghouse Filament LED or Timeless lamps for the vintage look you want.



†81022  
**Champagne Glass  
 Wide Rippled Shade Kit  
 with Adapters**  
 Fitter: 2.25"  
 Height: 5.51"  
 Diameter: 7.75"



†81025  
**White Opal  
 Schoolhouse Shade Kit  
 with Adapters**  
 Fitter: 2.25"  
 Height: 7.01"  
 Diameter: 10"



†81024  
**Diamond Cut  
 Clear Glass Globe Kit  
 with Adapters**  
 Fitter: 2.25"  
 Height: 8.27"  
 Diameter: 7.68"



†Adapters included to allow shades to fit 2¼" fitter pendants.  
 (Antique Brass and Oil Rubbed Bronze Finishes)




## RETRO SHADE ASSORTMENT

**81019**  
**Matte Black**  
**Globe Cage Shade**  
 Fitter: 2.25"  
 Height: 7"  
 Diameter: 8"



**81023**  
**Matte Black Angled**  
**Bell Cage Shade**  
 Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 7.60"



**85031**  
**Brushed Nickel Finish**  
**Cage Shade with**  
**Closed Bottom**  
 Fitter: 2.25"  
 Height: 8"  
 Diameter: 6.75"



**New!**

**85052**  
**Brushed Nickel Finish**  
**Cage Shade with**  
**Latched Bottom**  
 Fitter: 2.25"  
 Height: 8.19"  
 Diameter: 6"



**85033**  
**Oil Rubbed Bronze Finish**  
**Cage Shade with**  
**Closed Bottom**  
 Fitter: 2.25"  
 Height: 8"  
 Diameter: 6.75"



**New!**

**85051**  
**Oil Rubbed Bronze Finish**  
**Cage Shade with**  
**Latched Bottom**  
 Fitter: 2.25"  
 Height: 8.19"  
 Diameter: 6"



**85036**  
**Brushed Nickel Finish**  
**Cage Shade with**  
**Open Bottom**  
 Fitter: 2.25"  
 Height: 6.25"  
 Diameter: 5.75"



**85038**  
**Oil Rubbed Bronze Finish**  
**Cage Shade with**  
**Open Bottom**  
 Fitter: 2.25"  
 Height: 6.25"  
 Diameter: 5.75"



 **Westinghouse**  
**VINTAGE LAMPS**

Add Westinghouse Filament LED or  
 Timeless lamps for the vintage look you want.

## 2¼" FITTER SHADES



**81018**  
**Glazed Ice**  
**Cubic Dome Shade**  
 Fitter: 2.25"  
 Height: 6"  
 Width: 5"



• **85012**  
**Charcoal Swirl**  
**Cubic Dome Shade**  
 Fitter: 2.25"  
 Height: 5.50"  
 Width: 5.50"

**New!**



• **85003**  
**White and Clear**  
**Etched Cylinder Shade**  
 Fitter: 2.25"  
 Height: 7.88"  
 Diameter: 4.80"



• **85005**  
**White Alabaster**  
**Large Cylinder Shade**  
 Fitter: 2.25"  
 Height: 7.88"  
 Diameter: 4.63"



**85046**  
**Frosted Flared**  
**Cone Shade**  
 Fitter: 2.25"  
 Height: 5.32"  
 Diameter: 6.14"



• **81003**  
**White Linen**  
**Barrel Shade**  
 Fitter: 2.25"  
 Height: 5.30"  
 Diameter: 4.92"



• **81407**  
**Garden Moss Shade**  
 Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 4.50"



• **81310**  
**Giraffe Spot Shade**  
 Fitter: 2.25"  
 Height: 5.38"  
 Diameter: 4.50"



• **81311**  
**Fire Pit Shade**  
 Fitter: 2.25"  
 Height: 5.38"  
 Diameter: 4.50"



• **81409**  
**Charcoal Swirl Shade**  
 Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 4.85"



• **81400**  
**Wildfire**  
**Cylinder Shade**  
 Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 4.75"



• **81404**  
**Marble**  
**Cylinder Shade**  
 Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 4.75"



• **85701**  
**Ice**  
**Cylinder Shade**  
 Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 4.75"



**85702**  
**Brushed Nickel**  
**Perforated Metal Shade**  
 Fitter: 2.25"  
 Height: 6.50"  
 Diameter: 5"



•85730  
**Fire Pit  
 Long Shade**  
 Fitter: 2.25"  
 Height: 8.50"  
 Diameter: 4.50"



•85724  
**Lunar Weave  
 Long Shade**  
 Fitter: 2.25"  
 Height: 7.75"  
 Diameter: 4.75"

**New!**



85050  
**Crystal Jewel  
 Elongated Shade**  
 Fitter: 2.25"  
 Height: 10"  
 Diameter: 6"



•81315  
**Clear with  
 Black Rope Shade**  
 Fitter: 2.25"  
 Height: 5.75"  
 Diameter: 4.63"



•81314  
**Clear with  
 White Rope Shade**  
 Fitter: 2.25"  
 Height: 5.75"  
 Diameter: 4.63"



•81005  
**Mocha Scavo Bell Shade  
 with Raised Band**  
 Fitter: 2.25"  
 Height: 5.70"  
 Diameter: 5"



•81410  
**Chocolate Drizzle  
 Shade**  
 Fitter: 2.25"  
 Height: 6.38"  
 Diameter: 4.38"



•81405  
**Van Gogh  
 Shade**  
 Fitter: 2.25"  
 Height: 6.25"  
 Diameter: 4.38"



•81413  
**Chili Pepper  
 Shade**  
 Fitter: 2.25"  
 Height: 6.25"  
 Diameter: 4.38"



•81412  
**Lunar Weave Shade**  
 Fitter: 2.25"  
 Height: 6"  
 Diameter: 5.38"



•85722  
**White Opal  
 Fluted Shade**  
 Fitter: 2.25"  
 Height: 5.50"  
 Diameter: 4.75"



•81364  
**Temptress  
 Red Shade**  
 Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 4"



•81427  
**Spice Swirl  
 Shade**  
 Fitter: 2.25"  
 Height: 5.75"  
 Diameter: 4.63"

•Hand Blown Glass

## 2¼" FITTER SHADES



•81208  
**White Angled  
 Design Shade**  
 Fitter: 2.25"  
 Height: 6.75"  
 Diameter: 3.75"



•81275  
**Indigo Blue Angled  
 Design Shade**  
 Fitter: 2.25"  
 Height: 6.75"  
 Diameter: 3.75"



•81363  
**Burnt Umber  
 Swirl Bell Shade**  
 Fitter: 2.25"  
 Height: 4.81"  
 Diameter: 5.38"



81265  
**Hand-Painted  
 Leaf Design Bell Shade**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5.38"



81272  
**Milky Scavo Bell Shade**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5.38"



81391  
**Antique  
 Smolder Bell Shade**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5.25"



81167  
**Brown Swirl Bell Shade**  
 Fitter: 2.25"  
 Height: 5.13"  
 Diameter: 5.88"



81119  
**Licorice  
 Marbleized Bell Shade**  
 Fitter: 2.25"  
 Height: 4.50"  
 Diameter: 4.75"



81422  
**Brown  
 Marbleized Bell Shade**  
 Fitter: 2.25"  
 Height: 4.65"  
 Diameter: 5.40"



•81353  
**Clear and White  
 Design Bell Shade**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5"



81277  
**Beveled  
 Clear Glass Bell Shade**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 4.88"



•81095  
**Clear  
 Seeded Bell Shade**  
 Fitter: 2.25"  
 Height: 5"  
 Diameter: 4.88"



81098  
**Milky  
 Scavo Bell Shade**  
 Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 5.50"



81279  
**Milky  
 Scavo Bell Shade**  
 Fitter: 2.25"  
 Height: 5.13"  
 Diameter: 5.13"





•81414  
**Linen Globe Shade**  
 Fitter: 2.25"  
 Height: 4.88"  
 Diameter: 5.25"



81257  
**Sandy Fluted Bell Shade**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 5.50"



•81356  
**Tortoise Bell Shade**  
 Fitter: 2.25"  
 Height: 5.38"  
 Diameter: 4.75"



81121  
**Square Tiffany Shade**  
 Fitter: 2.25"  
 Height: 5.13"  
 Diameter: 4.75"



81051  
**Frosted Etched Bell Shade**  
 Fitter: 2.25"  
 Height: 4.50"  
 Diameter: 4.75"



•81227  
**White Opal Bell Shade**  
 Fitter: 2.25"  
 Height: 4.75"  
 Diameter: 4.75"



81253  
**Frosted Bell Shade with Clear Square Design**  
 Fitter: 2.25"  
 Height: 4.63"  
 Diameter: 5.38"



81479  
**Crystal Clear Pleated Shade**  
 Fitter: 2.25"  
 Height: 5"  
 Diameter: 4.25"



81094  
**Frosted Pleated Shade**  
 Fitter: 2.25"  
 Height: 5"  
 Diameter: 4.25"



81258  
**Clear Ribbed Bell Shade**  
 Fitter: 2.25"  
 Height: 4.50"  
 Diameter: 4.75"



81066  
**Frosted Ribbed Bell Shade**  
 Fitter: 2.25"  
 Height: 4.50"  
 Diameter: 4.75"

## 2¼" FITTER SHADES



**81242**  
**Satin**  
**Crimp Shade**  
 Fitter: 2.25"  
 Height: 4.13"  
 Diameter: 5"



• **81282**  
**Frosted Etched Grape**  
**Design Crimp Shade**  
 Fitter: 2.25"  
 Height: 4.81"  
 Diameter: 4.25"



• **81082**  
**Clear and Frosted with**  
**Gold Band Crimp Shade**  
 Fitter: 2.25"  
 Height: 5.13"  
 Diameter: 5.75"

• **85282**  
**6-Pack of 81282**



**81270**  
**Frosted and**  
**Clear Cross Shade**  
 Fitter: 2.25"  
 Height: 5.25"  
 Diameter: 5"



**81097**  
**Frosted Pleated**  
**Shade**  
 Fitter: 2.25"  
 Height: 5"  
 Diameter: 4.25"



**81365**  
**Parchment Leaf**  
**Shade**  
 Fitter: 2.25"  
 Height: 4.50"  
 Diameter: 6"



**81355**  
**Clear Prismatic**  
**Shade**  
 Fitter: 2.25"  
 Height: 3.75"  
 Diameter: 6.50"



**81382**  
**Linen Pendant**  
**Shade**  
 Fitter: 2.25"  
 Height: 5"  
 Diameter: 7.75"



**81120**  
**Cappuccino Swirl**  
**Shade**  
 Fitter: 2.25"  
 Height: 4.25"  
 Diameter: 6.88"



**81333**  
**Honey Swirl**  
**Scavo Shade**  
 Fitter: 2.25"  
 Height: 4.38"  
 Diameter: 6.88"

# CHIMNEYS



• **83070**  
**Clear**  
**Glass Chimney**  
*Fitter: 2.63"*  
*Height: 8.50"*  
*Bulge: 3.63"*  
*Top Opening: 2"*



• **83071**  
**3/4 Frosted**  
**Glass Chimney**  
*Fitter: 2.63"*  
*Height: 8.50"*  
*Bulge: 3.63"*  
*Top Opening: 2"*



• **81169**  
**Clear Flare Shade**  
*Fitter: 1.63"*  
*Height: 6.75"*  
*Diameter: 3.75"*



• **81160**  
**Clear Flare Shade**  
*Fitter: 1.63"*  
*Height: 6.50"*  
*Diameter: 3.63"*



• **81162**  
**Clear Williamsburg**  
**Style Shade**  
*Fitter: 1.63"*  
*Height: 6.50"*  
*Diameter: 3.75"*

• **85162**  
**6-Pack of 81162**



• **83090**  
**Clear**  
**Glass Chimney**  
*Fitter: 3"*  
*Height: 8.50"*  
*Bulge: 4"*  
*Top Opening: 2"*



• **83091**  
**3/4 Frosted**  
**Glass Chimney**  
*Fitter: 3"*  
*Height: 8.50"*  
*Bulge: 4"*  
*Top Opening: 2"*



• **83062**  
**Clear**  
**Glass Chimney**  
*Fitter: 2.63"*  
*Height: 7.50"*  
*Bulge: 3.50"*  
*Top Opening: 1.63"*



• **83063**  
**3/4 Frosted**  
**Glass Chimney**  
*Fitter: 2.63"*  
*Height: 7.50"*  
*Bulge: 3.50"*  
*Top Opening: 1.63"*



• **83102**  
**Clear**  
**Glass Chimney**  
*Fitter: 3"*  
*Height: 10"*  
*Bulge: 3.63"*  
*Top Opening: 2"*



• **83072**  
**Clear**  
**Glass Chimney**  
*Fitter: 2.63"*  
*Height: 10"*  
*Bulge: 3.63"*  
*Top Opening: 2"*



• **83100**  
**Clear**  
**Glass Chimney**  
*Fitter: 3"*  
*Height: 10"*  
*Bulge: 4"*  
*Top Opening: 2"*



• **83101**  
**3/4 Frosted**  
**Glass Chimney**  
*Fitter: 3"*  
*Height: 10"*  
*Bulge: 4"*  
*Top Opening: 2"*

• Hand Blown Glass


## GLASS DIFFUSERS



**81720**  
**White Diffuser**  
 Square: 12"  
 Depth: 1.50"



**81800**  
**Clear Wheat Design  
 on White Ruffled Edge  
 Diffuser**  
 Square: 12"  
 Depth: 1.50"



**81807**  
**Clear Floral Design  
 on White Diffuser**  
 Square: 12"  
 Depth: 1.50"



**81810**  
**Clear Floral Design  
 on White Diffuser**  
 Square: 14"  
 Depth: 1.75"



**81727**  
**Gloss White  
 Diffuser**  
 Diameter: 12"  
 Depth: 1.75"



**81925**  
**White Smooth Scavo  
 Diffuser**  
 Diameter: 13"  
 Depth: 1.75"



**81819**  
**Clear Dot Pattern  
 Diffuser**  
 Diameter: 13"  
 Depth: 1.25"



**81805**  
**Clear Dot Pattern  
 Diffuser**  
 Diameter: 15"  
 Depth: 1.50"



**81770**  
**Clear Wheat Design  
 on White Diffuser**  
 Diameter: 13"  
 Depth: 2.13"



**81837**  
**Frosted Diffuser**  
 Diameter: 12.75"  
 Depth: 2.38"





• **81578**  
**Opal**  
**Schoolhouse Shade**  
*Fitter: 4"*  
*Height: 6.25"*  
*Diameter: 7.25"*

• **85578**  
**6-Pack of 81578**



• **81528**  
**Opal**  
**Schoolhouse Shade**  
*Fitter: 4"*  
*Height: 7"*  
*Diameter: 8.50"*

• **85528**  
**6-Pack of 81528**



• **81592**  
**White**  
**Schoolhouse Shade**  
*Fitter: 3.25"*  
*Height: 4.94"*  
*Diameter: 5.75"*



• **81290**  
**Schoolhouse**  
**with Ridged Design**  
**Shade**  
*Fitter: 4"*  
*Height: 5"*  
*Diameter: 8"*



• **83757**  
**White Mushroom Shade**  
*Fitter: 8"*  
*Height: 4"*  
*Diameter: 9.50"*



• **81613**  
**White Mushroom Shade**  
*Fitter: 6"*  
*Height: 3.75"*  
*Diameter: 7.50"*



• **81620**  
**Grape Satin**  
**Mushroom Shade**  
*Fitter: 6"*  
*Height: 3.50"*  
*Diameter: 7.50"*

• **85757**  
**6-Pack of 83757**

• **85613**  
**6-Pack of 81613**



**85606**  
**White and Clear**  
**Drum Shade**  
*Fitter: 6"*  
*Height: 3.38"*  
*Diameter: 6.50"*  
**Sold as 6-Pack Only**



**85608**  
**White and Clear**  
**Drum Shade**  
*Fitter: 8"*  
*Height: 4"*  
*Diameter: 7.63"*  
**Sold as 6-Pack Only**



**81609**  
**White and Clear**  
**Drum Shade**  
*Fitter: 10"*  
*Height: 4.25"*  
*Diameter: 11"*

## GLASS GLOBES 3¼" &amp; 4" FITTERS



**85602**  
**Clear Design**  
**Shade**  
*Fitter: 3.25"*  
*Height: 5.75"*  
*Diameter: 5.50"*  
**Sold as 6-Pack Only**



**85612**  
**Frosted and Clear**  
**Shade**  
*Fitter: 3.25"*  
*Height: 5"*  
*Diameter: 6"*  
**Sold as 6-Pack Only**



• **81501**  
**Opal**  
**Globe**  
*Fitter: 3.25"*  
*Diameter: 6"*



• **81571**  
**Gloss White**  
**Globe**  
*Fitter: 4"*  
*Diameter: 8"*  
**85571**  
**6-Pack of 81571**



• **81570**  
**Gloss White**  
**Globe**  
*Fitter: 3.25"*  
*Diameter: 6"*  
**85570**  
**6-Pack of 81570**



• **81560**  
**Clear Seeded**  
**Globe**  
*Fitter: 3.25"*  
*Diameter: 6"*



• **85707**  
**Frosted Victorian**  
**Globe**  
*Fitter: 3.25"*  
*Diameter: 6"*  
**Sold as 6-Pack Only**  
**81575**  
*Fitter: 4"*  
*Diameter: 7.50"*



• **81574**  
**Cloudy Frosted**  
**Globe**  
*Fitter: 3.25"*  
*Diameter: 6"*



• **81549**  
**Gloss Clear**  
**Globe**  
*Fitter: 4"*  
*Diameter: 7.50"*



• **85712**  
**Gloss Clear**  
**Lustre Globe**  
*Fitter: 3.25"*  
*Diameter: 6"*  
**Sold as 4-Pack Only**



• **85705**  
**Smoke Lustre**  
**Globe**  
*Fitter: 3.25"*  
*Diameter: 6"*  
**Sold as 6-Pack Only**



**81254**  
**Clear Prismatic**  
**Globe**  
*Fitter: 3.25"*  
*Diameter: 6.38"*  
**85254**  
**6-Pack of 81254**



**85338**  
**Clear Prismatic**  
**Globe**  
*Fitter: 4"*  
*Diameter: 8"*  
**Sold as 6-Pack Only**

# POLYCARBONATE & ACRYLIC SHADES

**81918**  
**Drum Lens White Acrylic Shade**  
Notched Fitter: 9.88"  
Height: 2.50"  
Diameter: 11"



**81919**  
**Drum Lens White Acrylic Shade**  
Fitter: 12.63"  
Height: 2.50"  
Diameter: 13.75"



**81450**  
**White Glass Threaded Neck Globe**  
Thread: 3.25"  
Diameter: 6"



**81877**  
**White Polycarbonate Threaded Neck Globe**  
Thread: 3.25"  
Diameter: 6"



**81883**  
**White Acrylic Neckless Globe**  
Diameter: 12"  
Opening: 5.25"

**85450**  
**6-Pack of 81450**

**81887**  
**White Polyethylene Threaded Neck Globe**  
Thread: 3.25"  
Diameter: 6"

**81884**  
Diameter: 14"  
Opening: 5.25"



**81905**  
**White Polyethylene Globe**  
Fitter: 3"  
Diameter: 6"



**81869**  
**White Polycarbonate Globe**  
Fitter: 3.25"  
Diameter: 6"



**81900**  
**White Acrylic Globe**  
Fitter: 4"  
Diameter: 7.95"

**85869**  
**6-Pack of 81869**

**81901**  
Fitter: 4"  
Diameter: 10"

## ASSORTED SHADES, FITTERS &amp; CHANNELS



**81459**  
**White Tapered Polycarbonate Threaded Neck Shade**  
 Thread: 3.25"  
 Height: 6.25"  
 Diameter: 4"



**81457**  
**White Tapered Polycarbonate Threaded Neck Shade**  
 Thread: 3.25"  
 Height: 8.50"  
 Diameter: 4"



**81876**  
**Clear Tapered Polycarbonate Threaded Neck Shade**  
 Thread: 3.25"  
 Height: 8.75"  
 Diameter: 4"



**81452**  
**Vapor Proof Clear Glass Threaded Neck Shade**  
 Thread: 3.25"  
 Height: 6"  
 Diameter: 3.50"



• **81151**  
**Satin White Glass Shade**  
 Fitter: 2"  
 Height: 5"  
 Diameter: 4.75"



• **81100**  
**Frosted Etched Glass Shade**  
 Fitter: 1.63"  
 Height: 5"  
 Diameter: 4.25"



**85617**  
**Clear Glass Shade**  
 Fitter: 3.25"  
 Height: 4.75"  
 Diameter: 3.63"  
**Sold as 6-Pack Only**



• **81230**  
**Green with White Interior Glass Shade**  
 Height: 3.13"  
 Width: 8.75"  
 Depth: 5"  
 1/2" holes on both sides

• **85151**  
**6-Pack of 81151**

• **85100**  
**6-Pack of 81100**



**85604**  
**White Grooves with Clear Bottom Glass Shade**  
 Fitter: 3.25"  
 Height: 4.50"  
 Length: 5.75"  
**Sold as 6-Pack Only**



**81760**  
**White Glass Channel**  
 Length: 24"  
 Width: 3.75"  
 Depth: 3"  
 Hole Size: .38"  
 2 Holes  
 6 1/2" from ends  
 11" between holes



**81764**  
**White Glass Channel**  
 Length: 15"  
 Width: 3.75"  
 Depth: 3"  
 Hole Size: .38"  
 Centered Hole



**81759**  
**White Glass Channel**  
 Length: 12"  
 Width: 3.75"  
 Depth: 3"  
 Hole Size: .38"  
 Centered Hole



**81758**  
**White Glass Channel**  
 Length: 7.50"  
 Width: 3.75"  
 Depth: 3"  
 Hole Size: .38"  
 Hole 1.75" from end



# CLIP-ON SHADES



## CREATE A FIXTURE INSTANTLY!

Clip-on shades are a quick and easy way to change a light bulb into a fixture!  
Instantly add a decorative touch!



**81493**  
**Acrylic Prismatic Dome  
Clip-On Shade**  
Height: 4.75"  
Diameter: 8"



**81499**  
**Polypropylene Satin Tulip  
Clip-On Shade**  
Height: 4.75"  
Diameter: 8"




**81514**  
**Acrylic White Dome  
Clip-On Shade with  
Pull Chain Opening**  
Height: 4.75"  
Diameter: 7.75"



**81494**  
**Acrylic White Dome  
Clip-On Shade**  
Height: 4.75"  
Diameter: 7.75"

# GLASSWARE GLOSSARY



## FITTER (F)

Fitter size is the diameter of the glass where the glass attaches to the fixture or lamp.

## HEIGHT (H)

Distance between the two farthest points opposite each other on the top and bottom of the glass that form a vertical line.

## DIAMETER (D)

Distance between two opposite points at the widest part of the glass that form a horizontal line.

## CENTER HOLE

The opening on a neckless shade and measured like a fitter. If a piece of glass has a fitter and a center hole, the center hole is used for lock-up.

## DEPTH

Distance from the center point inside the glass to the point directly opposite, this is measured without mounting.

## BULGE

The diameter measured at the widest part of a chimney.

## TOP OPENING

Distance between the two farthest points opposite each other on the top of a student shade. All top openings are wide enough and made to fit over the average chimney.

## THREADED NECK

A fitter that attaches to the fixture or lamp by means of threads in the glass.

## NOTCHED FITTER

Designed to lock tightly into specially designed holders with ¼ turn.

# PLASTIC MATERIAL GUIDE

## FEATURE COMPARISON CHART

Feature	Polyethylene	Acrylic	Polycarbonate
Heat Resistance	G	G	E
Quality of Seams	F	E	E
UV Resistance	F	E	F
Strength	G	G	E
Light Transmission	F	E	G
Wall Thickness Uniformity	G	G	E
Shatter Resistance	E	F	G
Surface Characteristics	G	E	G
Appearance vs. Time	G	E	G
Strength vs. Time	G	E	F
Overall Appearance	G	E	G

KEY:  
 E = Excellent  
 G = Good  
 F = Fair


## RECOMMENDED MAXIMUM INCANDESCENT WATTAGE RATINGS

Polyethylene	
Globe	Watts
6"	40
8"	75
10"	100
12"	150
14"	200
16"	200
18"	250
—	—
—	—

Acrylic	
Globe	Watts
6"	60
8"	75
10"	100
12"	150
14"	150
16"	200
18"	200
Cylinder	Watts
5"	60

Polycarbonate	
Globe	Watts
6"	75
Cylinder	Watts
5½"	60
5¾"	60
6¼"	60
7¼"	60
8½"	60
8¾"	60
—	—

This wattage guide is a general recommendation only. Actual wattage ratings are influenced by fixture type, bulb location and ambient temperature. The light source should be located at the center of each shade.



## LIGHTING HARDWARE BULK & PACKAGED

For every repair or replacement need, Westinghouse has you covered. From sockets to switches, canopies to crossbars, we have the hard-to-find parts required to make your fixtures perform like new.

# GLASS SHADE HOLDER KITS & ACCESSORIES

## Glass Shade Holder Kits

Use (1) Medium Base Lamp,  
60 Watt Maximum

Includes:

- 1 Crossbar
- 2 Mounting Screws
- 1 Green Grounding Screw
- 3 Knurled Fitter Screws
- 1 Fiberglass Insulator



70231 - Brass Finish  
70243 - Antique Brass Finish  
70238 - White Finish  
4" Holder



70242 - Brass Finish  
3/4" Shade Holder with  
On/Off Pull Chain Switch



70230 - Brass Finish  
70236 - Antique Brass Finish  
3/4" Shade Holder

## 70234 Twin Cluster Ceiling Kit Medium Base

Includes:

- 1 Canopy
- 1 Wired Socket
- 1 Crossbar
- 2 Mounting Screws
- 1 Lock-Up Cap
- 2 Rubber Washers
- Ideal for Glass Diffusers



\* 22259  
Twin Cluster Socket  
with Male Threads  
on Each End  
Medium Base  
6" Wire Leads  
18 Gauge,  
105° Leads  
660 Watts Max.  
250 Volts  
1/8-IP Nipple  
Height - 4 3/8"



\* 22256  
3 Light Cluster Socket  
with Male Threads  
on Each End  
Medium Base  
6" Wire Leads  
18 Gauge  
105° Leads  
660 Watts Max.  
250 Volts  
1/8-IP Nipple  
Height - 4 3/4"





# SOCKETS



**\* 22207**  
**2-Piece Phenolic Shell**  
 On/Off  
 Medium Base  
 Nipple 1/8-IP  
 660 Watts Max.  
 250 Volts  
 Height - 2 3/4"



**\* 22205**  
**1-Piece Phenolic Shell**  
 Bottom Turn Knob Socket  
 Medium Base  
 Nipple 1/8-IP  
 660 Watts Max.  
 250 Volts  
 Height - 3 1/4"



**70430**  
**Turn Knob Phenolic Socket**  
 On/Off  
 Threaded 1/8-IP  
 Medium Base  
 660 Watts Max.  
 250 Volts



**\* 22234**  
**High Heat Phenolic**  
 On/Off  
 Medium Base  
 Keyless  
 Bushing 1/8-IP with Set Screw  
 660 Watts Max.  
 250 Volts  
 Height - 2 3/4"



**70146**  
**Vertical Phenolic Snap-In Socket**  
 Fits into 3/8" x 1/4" Hole  
 Medium Base  
 660 Watts Max.  
 250 Volts



**70145**  
**Horizontal Phenolic Snap-In Socket**  
 Fits into 7/8" x 1/4" Hole  
 Medium Base  
 660 Watts Max.  
 250 Volts



**70407**  
**Keyless Phenolic Socket**  
 1/8-IP Hickey  
 Medium Base  
 660 Watts Max.  
 250 Volts



**\* 22237**  
**Push-Through Phenolic**  
 Medium Base  
 1/8-IP Cap with Side Screw  
 Aluminum Screw Shell  
 660 Watts Max.  
 250 Volts  
 Height - 2 5/8"



**70433**  
**Pull Chain Phenolic Socket**  
 On/Off  
 Tapped 1/8-IP  
 Medium Base  
 250 Watts Max.  
 250 Volts



**\* 22501**  
**Push-Through**  
 Medium Base  
 660 Watts Max.  
 250 Volts  
 Height - 1 1/16"



**\* 22503**  
**Pull Chain**  
 On/Off  
 Medium Base  
 250 Watts Max.  
 250 Volts  
 Height - 1 3/4"



**\* 22502**  
**Turn Knob**  
 On/Off  
 Medium Base  
 250 Watts Max.  
 250 Volts  
 Height - 1 1/16"



**\* 22504 - 3-Way**  
**22505 - 2-Circuit Turn Knob**  
 Medium Base  
 250 Watts Max.  
 250 Volts  
 Height - 1 1/16"

CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# SOCKETS

- \* 22381 - 3 Light
- \* 22382 - 4 Light
- Black Harness Set**
- Candelabra Base
- Fits 3/4" Hole
- Includes Lock Nuts
- SPT-2, 18 Gauge,
- 105° Leads
- 75 Watts Max. Per Socket
- 125 Volts
- 6 1/4" Between Sockets
- 12" on End Height - 1/4"



- \* 22380
- 1 Light**
- Harness Set**
- Candelabra Base
- Fits 3/4" Hole
- Includes Lock Nut
- 12" Wire Leads
- SPT-2, 18 Gauge,
- 105° Leads
- 75 Watts Max., 125 Volts
- Height - 1/4"



- \* 22377
- Socket**
- 18" Wire Leads
- Candelabra Base
- 1/8-IP Hickey
- 18 Gauge,
- 105° Leads
- 75 Watts Max.,
- 125 Volts
- Height - 1 3/4"



- \* 22220
- Pigtail**
- 24" Wire Leads
- Candelabra Base
- 18-2, SPT-1
- 105° Leads
- 75 Watts Max.
- 125 Volts
- Height - 1 1/8"



- \* 22223
- Snap-In Pigtail**
- 24" Wire Leads
- Candelabra Base
- Snaps Into
- 1" Diameter Hole
- 18-2, SPT-1,
- 105° Leads
- 75 Watts Max.
- 125 Volts
- Height - 1 1/8"



- \* 22215
- Socket**
- 6" Wire Leads and
- Straight Bracket
- Medium Base
- 18 Gauge, 105° Leads
- Bracket Extends 1 5/8"
- Measured Center to Center
- 660 Watts Max.
- 250 Volts
- Height - 1 1/2"



- \* 22216
- Socket**
- 9" Wire Leads
- Medium Base
- 1/8-IP Hickey
- 18 Gauge,
- 105° Leads
- 660 Watts Max.
- 250 Volts
- Height - 1 3/8"



- \* 22200
- Pin Type With Cap**
- Candelabra Base
- Use with SPT-1 Wire
- 75 Watts Max.
- 125 Volts
- Height - 1/4"



- \* 22213
- Snap-In Socket**
- 6" Wire Leads
- Medium Base
- Fits 1 1/4" Hole
- 18 Gauge,
- 105° Leads
- 660 Watts Max.
- 250 Volts
- Height - 1 1/2"



- \* 22214
- Snap-In Socket**
- 6" Wire Leads and
- Ground Wire
- Medium Base
- Fits 3/8" x 1/4" Hole
- 18 Gauge,
- 105° Leads
- 660 Watts Max.
- 250 Volts
- Height - 2"



- \* 22217
- Snap-In Socket**
- 9" Wire Leads
- Medium Base
- Fits 3/8" x 1/4" Hole
- 18 Gauge,
- 105° Leads
- 660 Watts Max.
- 250 Volts
- Height - 1 1/2"



- \* 22222
- Pin-Type Socket with**
- Hanger Bracket**
- Medium Base
- Use with SPT-2 Wire
- 660 Watts Max.
- 250 Volts
- Height - 2"

\*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY.

# SOCKETS



70412 - 3-Way  
70413 - On/Off  
70421 - 2 Circuit  
**Turn-Knob Socket**  
Brass Finish  
Medium Base  
Tapped 1/8-IP  
250 Watts Max., 250 Volts



70406  
**3-Way Turn-Knob Socket**  
Brushed Nickel Finish  
Medium Base  
Tapped 1/8-IP  
250 Watts Max., 250 Volts



70415  
**3-Way Turn-Knob Socket**  
Bronze Finish  
Medium Base  
Tapped 1/8-IP  
250 Watts Max., 250 Volts



70410 - Brass Finish  
\*22011 - Polished Brass  
**Push-Through Socket with Set Screw**  
On/Off  
Brass Finish  
Medium Base  
Tapped 1/8-IP  
660 Watts Max., 250 Volts



70411 - On/Off  
70431 - 3-Way  
**Pull Chain Socket**  
Brass Finish  
Medium Base  
Tapped 1/8-IP  
250 Watts Max., 250 Volts




NO TERMINAL SCREWS

70417  
**Quick-Snap 3-Way Turn-Knob Socket**  
Brass Finish  
Medium Base  
Tapped 1/8-IP  
250 Watts Max., 250 Volts



\* 22001 - Brite Gilt  
\* 22003 - Brass Finish  
**Keyless Socket**  
Medium Base  
Bushings 1/8-IP with Set Screw  
660 Watts Max., 250 Volts  
Height - 2"



\* 22031 - Polished Brass  
**Turn-Knob Socket**  
Medium Base  
Bushings 1/8-IP with Set Screw  
Removable Knob  
250 Watts Max., 250 Volts  
Height - 2 1/2"



\* 22041 - Polished Brass  
**3-Way Turn-Knob Socket**  
Medium Base  
Bushings 1/8-IP with Set Screw  
Removable Knob  
250 Watts Max., 250 Volts  
Height - 2 1/2"



\* 22051 - Polished Brass  
**2 Circuit Turn-Knob Socket**  
Medium Base  
Bushings 1/8-IP with Set Screw  
Removable Knob  
250 Watts Max., 250 Volts  
Height - 2 1/2"

CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# KEYLESS SOCKETS & ACCESSORIES



**\*22125**  
**1 1/2" Keyless Socket**  
 Candelabra Base  
 1/8-IP Hickey  
 75 Watts Max., 125 Volts



**\*22126**  
**70403 (Carded 2-Pack)**  
**2" Keyless Socket**  
 Candelabra Base  
 1/8-IP Threaded Hickey  
 75 Watts Max., 125 Volts



**\*22136**  
**3" Keyless Socket**  
 Medium Base  
 1/8-IP Hickey  
 660 Watts Max., 250 Volts



**\*22138**  
**Adjustable Keyless Socket**  
 Medium Base  
 1/8-IP Hickey  
 660 Watts Max., 250 Volts  
 Height Adjustable from 4" - 5 5/8"



**\*22127**  
**70402 (Carded 2-Pack)**  
**Adjustable Keyless Socket**  
 Candelabra Base  
 1/8-IP Threaded Hickey  
 75 Watts Max., 125 Volts  
 Height Adjustable from 3 1/4" - 4 3/4"



**70161**  
**Two Replacement Knobs**  
 Black Finish  
 With 1/2" Extensions  
 Tapped 5/16"-F x 1/16"-M



**\*22551**  
**Replacement Paper Shell**  
 For Turn Knob or Pull Chain Sockets



**70160**  
**Two Socket Keys**  
 Brass Finish  
 With 1/2" Extensions  
 Tapped 5/16"-F x 1/16"-M



# PORCELAIN FIXTURE SOCKETS



**70409**  
**Porcelain Keyless Socket**  
 Medium Base  
 Height - 2"  
 1/8-IP Threaded Cap  
 660 Watts Max.  
 250 Volts



**70408**  
**Porcelain Keyless Socket Adapter Kit**  
 1/8-IP Threaded Cap  
 660 Watts Max.  
 250 Volts

- Includes:
- 1 Medium Base Socket
  - 1 Screw Collar Loop
  - 1 Fiber Washer
  - 1 Locknut
  - 1/8-IP x 1" Nipple
  - 1/8-IP x 2" Nipple



**70419**  
**Porcelain Socket**  
 Candelabra Base  
 10" Wire Leads  
 Height - 1 7/8"  
 Diameter - 1"  
 1/8-IP Hickey  
 18 Gauge, 105° Leads  
 75 Watts Max.  
 125 Volts



**\*22370**  
**77077**  
**70425**  
**Porcelain Fixture Socket**  
 Medium Base  
 10" Wire Leads  
 Height - 2.41"  
 1/8-IP Hickey  
 18 Gauge, 105° Leads  
 660 Watts Max.  
 250 Volts



**\*22212**  
**70424**  
**Porcelain Snap-In Socket**  
 Medium Base  
 Fits 1 1/2" Hole  
 6" Wire Leads  
 Height - 1 3/4"  
 18 Gauge, 125° Leads  
 660 Watts Max.  
 250 Volts



**\*22272**  
**70429**  
**Porcelain Threaded Socket with Steel Shade Ring**  
 Medium Base  
 Bushing 1/8-IP with Set Screw  
 Height - 2 1/8"  
 Ring Size - 2 1/4"  
 660 Watts Max.  
 250 Volts



**\*22371**  
**70426**  
**Porcelain Fixture Socket**  
 Medium Base  
 Height - 2"  
 1/4-IP Hickey  
 660 Watts Max.  
 250 Volts



**70010**  
**Porcelain Threaded Socket with Aluminum Shade Ring**  
 Medium Base  
 Height - 1 5/8"  
 Ring Height - 1/2"  
 660 Watts Max.  
 250 Volts

CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# PORCELAIN SOCKETS & RECEPTACLES



**\* 22273**  
**One-Piece Receptacle**  
 Medium Base  
 600 Watts Max., 250 Volts  
 Height - 1½"  
 180° C Maximum Temp.



**\* 22150**  
**70364**  
**Socket Extender**  
 Medium Base  
 660 Watts Max., 250 Volts  
 Extension - ¼"  
 Overall Length - 2¼"



**\* 22218**  
**Keyless Socket**  
**One Screw Surface Mount**  
 Medium Base  
 7" Wire Leads  
 660 Watts Max., 250 Volts  
 105° Leads  
 Leads Height - 1½"



**\* 22372**  
**Snap-In**  
**Porcelain Socket**  
 Medium Base  
 9" Wire Leads  
 Fits ¾" x ¼" Hole  
 18 Gauge, 105° Leads  
 660 Watts Max., 250 Volts  
 Height - 2"



**\* 22276**  
**Snap-In**  
**Porcelain Socket**  
 Medium Base  
 660 Watts Max., 250 Volts  
 Height - 1¾"



**\* 22281**  
**Mogul Base Socket**  
 3-Way  
 Removable Knob  
 Bushing ¼-IP  
 750 Watts Max., 250 Volts  
 Height - 4¼"



**\* 22282**  
**Mogul Base Socket**  
 1500 Watts Max., 600 Volts  
 Height - 2¾"  
 4KV Pulse Rating



**\* 22266**  
**Two-Piece**  
**Sign Receptacle**  
 Medium Base  
 660 Watts Max., 250 Volts  
 Height - 1½"  
 300° C Maximum Temp.

# SOCKETS, SOCKET REDUCERS & SHADE RINGS




**\* 22274**  
**Keyless Twin Socket**  
 Medium Base  
 Bushing 1/8-IP  
 With Set Screw  
 660 Watts Max.  
 250 Volts  
 Height - 2 1/8"




**\* 22267**  
**Keyless Socket**  
 Medium Base  
 1/8-IP Hickey  
 660 Watts Max.  
 250 Volts  
 Height - 2"  
 1875 Pulse Rated



**\* 22269**  
**Keyless Socket**  
 Medium Base  
 Bushing 1/8-IP  
 With Set Screw  
 660 Watts Max.  
 250 Volts  
 Height - 2"




**\* 22402**  
**Socket Adapter Reducer**  
 Reduces German or Italian Base to Candelabra Size  
 With Rubber Ring  
 75 Watts Max.  
 120 Volts



**\* 22403**  
**Socket Adapter Reducer**  
 Reduces Intermediate Base to Candelabra Base  
 With Rubber Ring  
 75 Watts Max.  
 120 Volts



**\* 22406**  
**Socket Adapter Reducer**  
 Reduces Mogul Base to Medium Base  
 660 Watts Max.  
 250 Volts



**\* 22411**  
**70361 Socket Adapter Enlarger**  
 Enlarges Candelabra Base to Medium Base  
 75 Watts Max.  
 125 Volts



**70428**  
**Steel Shade Ring For Medium Base Sockets**  
 Ring Size - 2 3/8"  
 Outside Diameter - 2 1/4"  
 Inside Diameter - 1 1/2"



**70001**  
**Two Aluminum Shade Rings For Medium Base Sockets**  
 Outside Diameter - 2"  
 Inside Diameter - 1 1/2"



**70435**  
**Phenolic Shade Ring For Medium Base Sockets**  
 Outside Diameter - 2 3/16"  
 Inside Diameter - 1 5/8"



**70000**  
**Steel Shade Ring Wrench with Black Rubber Handle**  
 For Medium Base Threaded Rings  
 Height: 4 3/4"

CARDED PRODUCT SOLD IN INNER PACK ONLY.

**\*Bulk Pack**

# SPECIALTY SOCKETS & LAMP HOLDERS



**\* 22471**  
**Mini BiPin Quartz MR16 Socket**  
 GX5.3 Base  
 12" 18 Gauge Leads  
 SF-1 200° C Leads  
 100 Watts Max., 250 Volts  
 Height - 1"



**\* 22470 - GY6.35 Base**  
**\* 22472 - GX5.3 Base**  
**Mini BiPin Quartz MR16 Socket**  
 12" 18 Gauge Leads  
 SF-1 200° C Leads  
 100 Watts Max., 250 Volts  
 Height - 3/8"




**\* 22481**  
**High Pressure Sodium Lamp Socket**  
 9" Wire Leads  
 Medium Base  
 SF-2/SEW-2 200° Leads  
 4 K.V. Pulse Rated  
 660 Watts Max., 600 Volts  
 1/2" Bushing  
 Height - 1 1/4"



**\* 22480**  
**High Pressure Sodium Lamp Socket**  
 9" Wire Leads  
 Medium Base  
 SF-2/SEW-2 200° Leads  
 4 K.V. Pulse Rated  
 660 Watts Max., 600 Volts  
 1/2" Screw-Down  
 Height - 1 1/4"



**22000**  
**Retrofit LED Adapter**  
 For use with  
 Recessed LED Downlights -  
 Item #'s: 31043, 31041, 31040, 31044,  
 31045, 31046, 41040, 41041, 31053,  
 31054, 31055 and 31056  
 GU24 Base  
 660 Watts Max., 250 Volts  
 Height - 7 1/2"



**\* 11110**  
**Quartz Lamp Holder**  
 5" Wire Leads  
 SF-1 200° C 300V Leads  
 For 4 5/8" Lamp  
 500 Watts Max.  
 250 Volts  
 Fits R7S, 4 5/8" Lamp Bases  
 Height - 1 3/8"



**\* 11104**  
**Porcelain Halogen Socket**  
 5" Wire Leads  
 SF-1 200° C 300V Leads  
 100 Watts Max., 250 Volts  
 Fits G4, GX5.3, GV5.3  
 and G6.35 Lamp Bases  
 Height - 3/8"



**\* 11107**  
**MR16 Porcelain Socket**  
 5" Wire Leads  
 SF-1 200° C Leads  
 75 Watts Max., 125 Volts  
 Fits G5.3, GU5.3  
 and GX5.3 Lamp Bases



**\* 11108**  
**MR16 Porcelain Socket**  
 5" Wire Leads  
 SF-1 200° C Leads  
 75 Watts Max., 300 Volts  
 Fits G5.3, GU5.3  
 and GZ5.3 Lamp Bases

\*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY.



# LAMP HOLDERS



**\* 22451**  
**Slimline Slide-On Lamp Holder**  
 Plunger Pedestal-Type  
 Shallow End  
 For T8 Lamps  
 660 Watts Max., 1000 Volts



**\* 22452**  
**Slimline Slide-On Lamp Holder**  
 Fixed Pedestal-Type  
 Shallow End  
 For T8 Lamps  
 660 Watts Max., 1000 Volts



**\* 22490**  
**Stationary End Lamp Holder**  
 For HO, VHO,  
 SHO Lamps  
 660 Watts Max., 1000 Volts



**\* 22491**  
**Plunger End Lamp Holder**  
 For HO, VHO,  
 SHO Lamps  
 660 Watts Max., 1000 Volts



**\* 22457**  
**Medium BiPin Lamp Holder**  
**Floating Action for U-Shape Lamps**  
 Low Profile Size  
 20 Gauge  
 660 Watts Max., 600 Volts



**\* 22458**  
**Medium BiPin Lamp Holder**  
**Floating Action for U-Shape Lamps**  
 Low Profile Size  
 Disconnect Feature Guards  
 Against Electric Shock  
 No. 18/20 Gauge  
 660 Watts Max., 600 Volts



**\* 22453**  
**Medium BiPin Lamp Holder**  
 Low Profile Size  
 660 Watts Max., 600 Volts  
 T8/T12 Non Shunted



**\* 22456**  
**Medium BiPin Turn Type Lamp Holder**  
 Standard Size  
 No. 18/20 Gauge  
 Panel Mount  
 660 Watts Max., 600 Volts



**\* 22454**  
**Medium BiPin Turn Type Lamp Holder**  
 Low Profile Size  
 No. 18/20 Gauge  
 Panel Mount, Captive  
 Mount and Screw  
 660 Watts Max., 600 Volts  
 Non Shunted



**Fluorescent Lamp Starters**  
**\* 22560 - FS-2 - RoHS Compliant**  
 14, 15 and 20 Watt Lamps  
**\* 22561 - FS-4 - RoHS Compliant**  
 30 and 40 Watt Lamps  
**\* 22562 - FS-5 - RoHS Compliant**  
 4, 6 and 8 Watt Lamps

CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# SWITCHES



**\* 22324 - Nickel Finish  
3-Way Canopy Switch  
With 4' White Braided Cord**  
6" Wire Leads  
18 Gauge, 105° Leads  
Fits 3/8" Hole  
1A, 125 VT  
3A, 250 VAC  
6A, 125 VL  
6A, 125 VAC  
Sequence of Operation:  
Low / Medium / High / Off  
Height - 1 3/16"



**\* 22320 - Nickel Finish, 3' Cord  
\* 22321 - Brass Finish, 4' Cord  
Pull Chain Canopy Switch  
With White Braided Cord**  
6" Wire Leads  
18 Gauge, 105° Leads  
Fits 3/8" Hole  
3A, 250 VAC  
6A, 125 VAC  
6A, 125 VL  
Height - 1 1/16"



**\* 22303 - Brass Knob  
Single Pole  
Rotary Switch With  
Removable Knob**  
6" Wire Leads  
18 Gauge, 105° Leads  
7/16" Nipple  
Fits 3/8" Hole  
1A, 125 VAC-L  
1A, 250 VAC  
3A, 120 VAC  
Height - 1 1/16"



**\* 22310  
3-Way, 2 Circuit  
Switch With  
Removable  
Brass Knob**  
6" Wire Leads  
18 Gauge, 105° Leads  
3/8" Nipple  
Fits 3/8" Hole  
3A, 250 Volts  
6A, 125 VT  
Sequence of Operation:  
1 On / 2 On / 1 & 2 On / Off  
Height - 1 1/4"



**\* 22306  
Push Canopy  
Switch**  
4 3/4" Wire Leads  
18 Gauge, 105° Leads  
Fits 3/8" Hole  
3A, 250 VAC  
6A, 125 VL  
6A, 125 VAC  
Height - 1 1/4"

# SWITCHES



**77022**  
**Fan Light Switch**  
 Chrome Pull Chain,  
 2 Wire, Single Pole Switch  
 3' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC



**77023**  
**Fan Light Switch**  
 Polished Brass Pull Chain,  
 2 Wire, Single Pole Switch  
 2' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC




**77287**  
**Fan Light Switch**  
 Antique Brass Pull Chain,  
 2 Wire, Single Pole Switch  
 3' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC




**70290**  
**Replacement Canopy Light Switch**  
 With Brass Pull Chain  
 3' Braided Cord  
 6" Wire Leads  
 Height - 1 1/4"  
 Fits 3/8" Hole



**77285 - 3-Wire Unit**  
**3-Way Fan Light Switch**  
 With Antique Brass Pull Chain,  
 2' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC



**77052 - 3-Wire Unit**  
**3-Way Fan Light Switch**  
 With Polished Brass Pull Chain,  
 2' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC



**77091**  
**Fan Capacitor**  
 3 MFD and 6.5 MFD  
 3-Wire 150V



**77288 - Dual Capacitor, 4-Wire Unit**  
**3-Speed Fan Switch**  
 With Antique Brass Pull Chain,  
 3' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC



**77286 - Single Capacitor, 4-Wire Unit**  
**3-Speed Fan Switch**  
 With Antique Brass Pull Chain,  
 3' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC



**77075 - With Polished Brass Pull Chain**  
**77073 - With Antique Brass Pull Chain**  
**3-Speed Fan Switch Triple Capacitor 8-Wire Unit**  
 2' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC



**77021 - Single Capacitor, 4-Wire Unit**  
**3-Speed Fan Switch**  
 With Polished Brass Pull Chain,  
 2' Braided Cord  
 3A, 250 VAC  
 6A, 125 VAC

CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# CROSSBARS

All crossbars are made of steel.



**\*21032**  
**70111**  
**Adjustable All-Purpose Crossbar**  
 Slips  $\frac{3}{8}$ -IP  
 Holes Tapped 8-32  
 Adjusts from 3 $\frac{3}{8}$ " to 5"  
 for Slot Mounting on 3",  
 3 $\frac{1}{4}$ " or 4" Box  
 Two  $\frac{1}{2}$ " Head Screws Included  
 Two  $\frac{1}{4}$ " Head Screws Included  
 35 lb. Load Rating



**70115**  
**Quick Assist Crossbar™**  
 Slips  $\frac{3}{8}$ -IP  
 45 lb. Load Rating  
 Patent # 6,824,298



**70112**  
**4" Offset Crossbar**  
 Two  $\frac{1}{2}$ " Mounting Screws  
 and Two Tapped  $\frac{5}{32}$  Holes  
 Spaced 2 $\frac{3}{4}$ " Apart  
 Slips  $\frac{3}{8}$ -IP  
 35 lb. Load Rating



**\*21003**  
**70113**  
**4" Long Crossbar**  
 Tapped  $\frac{1}{8}$ -IP  
 45 lb. Load Rating

**Quick Assist Crossbar™**  
 Patented Technology

- U-slot design allows for easy adjustments without rewiring.
- Pre-assemble fixture before installation.
- No threading required so wires never twist during assembly.



**70110**  
**4" Crossbar Kit**  
 Tapped  $\frac{1}{4}$ -IP  
 35 lb. Load Rating

- Includes:
- 1 Crossbar
  - 1  $\frac{3}{8}$ -IP x  $\frac{1}{4}$ -IP Reducing Hickey
  - 1  $\frac{1}{4}$ -IP x  $\frac{1}{8}$ -IP Reducing Bushing
  - 2 8-32 x  $\frac{1}{2}$ " Mounting Screws



**70350 - Brass Finish**  
**70352 - Antique Brass Finish**  
**Screw Collar Loop Kit**  
 Fits Canopies with a  $\frac{1}{16}$ " Center Hole  
 Tapped  $\frac{1}{4}$ -IP  
 35 lb. Load Rating

- Includes:
- 1 Crossbar
  - 1 Screw Collar Loop
  - 2 Locknuts
  - 1 Lock Washer
  - 1  $\frac{1}{4}$ -IP x  $\frac{1}{2}$ " Nipple
  - 1  $\frac{3}{8}$ -IP x  $\frac{1}{4}$ -IP Reducing Hickey
  - 2 8-32 x  $\frac{1}{2}$ " Mounting Screws



# CROSSBARS

All crossbars are made of steel.

**\*21030**

**Universal Crossbar**

Slips  $\frac{3}{8}$ -IP

Can Be Used for Porch Bracket, Ceiling Fixture  
or Any Other Type of Wall Mounted Lamp

Easily Adjustable for Slot Mounting

Two No. 10 Wood Screw Holes

Will Adjust on 3", 3 $\frac{1}{4}$ " or 4" Box 35 lb. Load Rating



**\*21006**

**70114**

**Offset Crossbar**

4" Long

8-32 Tapped Holes

Green Ground Screw

35 lb. Load Rating



**\*21038**

**Circular Crossbar**

4 Holes Tapped 8-32

2 $\frac{3}{4}$ " Center to Center

3 $\frac{1}{2}$ " Center to Center

45 lb. Load Rating



**\*21008**

**Crossbar**

3 $\frac{7}{8}$ " Long

Ground Screw Inserted

Tapped  $\frac{1}{4}$ -IP

45 lb. Load Rating



**\*21004**

**Crossbar**

4" Long

Tapped  $\frac{1}{8}$ -IP

Green Ground Screw

45 lb. Load Rating



**\*21005**

**Crossbar**

4" Long

Tapped  $\frac{1}{4}$ -IP

45 lb. Load Rating



**\*21036**

**Crossbar Extension End**

Tapped 8-32

Makes any crossbar adjustable.

The combined load rating is a maximum of 30 lbs. when  
used in conjunction with another crossbar.

# NIPPLES & ALL-THREAD PIPES

## THREAD SIZES

Thread sizes come in several different types:

- 1/4-27 is 1/4" in diameter and fits harps and most finials
- 1/8-IP is 3/8" in diameter and fits ordinary lamp sockets
- 1/4-IP is 1/2" in diameter and is used in floor lamps



**70151**  
**Six Assorted Nipples**  
 Zinc-Plated

- Includes:
- 2 1/4-IP x 3/4"
  - 2 1/4-IP x 1 1/2"
  - 2 1/4-IP x 2"



**70150**  
**Eight Assorted Nipples**  
 Zinc-Plated

- Includes:
- 2 1/8-IP x 1/2"
  - 2 1/8-IP x 1"
  - 2 1/8-IP x 1 1/2"
  - 2 1/8-IP x 2"


1/4-27




1/8-IP



1/4-IP



3/8-IP



**70613 - 6" Long (Carded 2-Pack)**  
**Steel Nipples**  
 Zinc-Plated  
 Threaded 1/4-IP



**\* 13352**  
**Brass Hex Head Nipple**  
 Threaded 1/8-IP  
 Thread 7/16" Long




**\* 13312 - 1 1/2" Long**  
**Brass Running Thread Nipples**  
 Threaded 1/8-IP



**Steel Nipples**  
 Zinc-Plated

- \* 13204 - 1/2" Long
  - \* 13206 - 3/4" Long
  - 70176 - 1" Long (Carded 4-Pack)
  - \* 13212 - 1 1/2" Long
  - 70601 - 1 1/2" Long (Carded 4-Pack)
  - \* 13216 - 2" Long
  - 70602 - 2" Long (Carded 2-Pack)
  - \* 13224 - 3" Long
  - 70603 - 3" Long (Carded 2-Pack)
  - \* 13232 - 4" Long
  - 70604 - 4" Long (Carded 2-Pack)
  - \* 13248 - 6" Long
  - 70606 - 6" Long (Carded 2-Pack)
- Threaded 1/8-IP



**\* 13650**  
**70270**  
**30" Steel Brass-Plated All-Thread Pipe**  
 Threaded 1/8-IP

**70272**  
**12" All-Thread Lamp Pipe Kit**  
 Zinc-Plated Steel

- Includes:
- 2 1/8-IP x 12" Threaded Pipe
  - 2 1/8-IP Couplings
  - 2 1/8-IP Locknuts
  - 2 1/8-IP Knurled Locknuts
  - 2 Washers

\*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY.

# ASSORTED HARDWARE



**\* 12060**  
**Hexagon**  
 Steel  
 Tapped ¼-IP  
 Diameter - 1/16"



**\* 12055**  
**Hexagon**  
 Steel  
 Tapped ½-IP  
 Diameter - 3/16"




**\* 11744**  
**Hexagon**  
 Brass  
 Tapped ½-IP  
 Diameter - 3/16"




**70162 - (Carded 2 Pack)**  
**Couplings**  
 Polished Brass  
 Tapped ½-IP



**70620**  
**Four Knurled Locknuts**  
 Solid Brass  
 Tapped ½-IP



**70621 - Solid Brass**  
**70622 - Steel**  
**Six Hex Nuts**  
 Tapped ½-IP



**70172**  
**Twelve Hex Nuts**  
 Solid Brass  
 Tapped ½-IP




**70155**  
**Twelve Assorted Washers**  
 Brass-Plated Steel  
 For ½-IP Nipples

- Includes:
- 4 Lock Washers
  - 4 Flat Washers
  - 4 Rubber Washers



**70628**  
**Six Assorted Nuts and Washers**  
 Brass-Plated Steel  
 For ½-IP Nipples

- Includes:
- 2 Lock Washers
  - 2 Flat Washers
  - 2 Hex Nuts



**70152**  
**Sixteen Assorted Hex Nuts**  
 Steel

- Includes:
- 4 8-32 Hex Nuts
  - 2 ¼-27 Hex Nuts
  - 6 ½-IP Hex Nuts
  - 2 ¼-IP Hex Nuts
  - 2 3/8-IP Hex Nuts



**70153**  
**Twelve Assorted Locknuts**  
 Solid Brass

- Includes:
- 2 8-32 Battery Nuts
  - 2 ¼-27 Threaded Knurled Locknuts
  - 2 ½-IP Knurled Locknuts
  - 4 ½-IP Hex Nuts
  - 2 ¼-IP Knurled Locknuts



**70638 - Brass Finish**  
**70639 - Nickel Finish**  
**Lock-Up Kits**  
 For Ceiling Glass  
 Tapped ½-IP



**70630**  
**Three Lock-Up Kits**  
 For Ceiling Glass  
 Tapped ½-IP  
 Includes:  
 • Brass, Brushed Nickel and Oil Rubbed Bronze Finishes



**70660**  
**Four Cap Nuts**  
 Solid Brass  
 Diameter - 3/8"  
 Tapped 8-32



**70663**  
**Six Cap Nuts**  
 Diameter - 3/8"  
 Tapped 8-32  
 Includes:  
 • 2 Brass Finish  
 • 2 Oil Rubbed Bronze Finish  
 • 2 Chrome Finish

CARDER PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# ASSORTED HARDWARE



**77016**  
**20 - 1/2" Knurled Head Screws**  
*Assorted for Fan Lights and Fan Blades*  
 Includes:  
 • 5 - 8-32 Antique Brass  
 • 5 - 8-32 Polished Brass  
 • 5 - 10-24 Antique Brass  
 • 5 - 10-24 Polished Brass



**70156**  
**Thirteen Assorted Screws**  
 Includes:  
 • 3 - 8-32 x 1/2" Brass-Plated  
 • 3 - 8-32 x 1/2" Nickel-Plated  
 • 3 - 8-32 x 3/4" Brass-Plated  
 • 2 - 8-32 x 1" Brass-Plated  
 • 2 - 8-32 x 2" Brass-Plated



**70635**  
**Fourteen Piece Metric Lighting Fixture Repair Kit**  
 Includes:  
 • 2 - 8-32 x 3/8" Philips Head Screws  
 • 2 - 8-32 x 1/2" Knurled Head Screws  
 • 2 - 8-32 x 5/8" Philips Head Screws  
 • 2 - 8-32 x 5/8" Knurled Head Screws  
 • 2 - 8-32 x 1" Cross Bar Screws  
 • 4 - 8-32 Knurled Knobs



**70632** - Brass-Plated - 1/2" Long  
**70633** - Nickel-Plated - 1/2" Long  
**70634** - Brass-Plated - 3/4" Long  
**Three Knurled Head Steel Screws**  
 8-32 Thread



**77047** - Polished Brass Finish  
**77048** - Antique Brass Finish  
**10 Piece Motor Screw Kit**  
*For Mounting Fan Blade Arms to Motor Housing*



**77040** - Polished Brass Finish  
**77041** - Antique Brass Finish  
**12 Fitter Screws**  
*For Fan Lights*



**70636**  
**Five Round Head Screws**  
*Brass-Plated Steel*  
 8-32 Thread x 2" Long

**\*21530**  
**1 5/16" Diameter Female Loop**  
*Brass-Plated and Lacquered*  
 Tapped 1/8-IP  
 45 lb. Load Rating  
 Hole for Wiring



**70254**  
**1 3/8" Diameter Female Loop**  
*Antique Brass Finish*  
 Tapped 1/8-IP  
 40 lb. Load Rating



**70258**  
**Two 1" Diameter Female Loops**  
*Brushed Nickel Finish*  
 Tapped 1/8-IP  
 45 lb. Load Rating



**70255**  
**Two 1" Diameter Female Loops**  
*Brass Finish*  
 Tapped 1/8-IP  
 45 lb. Load Rating



**70256**  
**Two 1" Diameter Female Loops**  
*Antique Brass Finish*  
 Tapped 1/8-IP  
 45 lb. Load Rating



**70250**  
**Two 1" Diameter Female and Male Loops**  
*Brass Finish*  
 1/8-IP Thread  
 45 lb. Load Rating



**70169** - Brass Finish  
**70640** - Nickel Finish  
**Two Lock-Up Caps**  
 Diameter - 5/16"  
 Tapped 1/8-IP



**70159** - Brass Finish  
**Two Lock-Up Caps**  
 Diameter - 1"  
 Tapped 1/8-IP



**70158** - White Finish  
**Two Lock-Up Caps**  
 Diameter - 1 1/16"  
 Tapped 1/8-IP



# BEADED CHAIN & CONNECTORS



**77046 - White**  
Six Beaded Chain Connectors



**77045 - Chrome**  
Six Beaded Chain Connectors



**\* 16572 - Brass**  
Beaded Chain Connector



**70661**  
Walnut Wooden Ball Pull Chain  
36" Polished Brass Beaded Chain



**77044 - Solid Brass**  
Six Beaded Chain Connectors



**77066 - Antique Brass**  
Six Beaded Chain Connectors



**\* 16576**  
Brass Finish End Bell  
For Beaded Chain or Pull Cord



**Beaded Chain**  
.011 Gauge 1/8" Diameter Ball 75 Balls per Foot

Item No.	Length	Finish
* 16565	Sold by Foot or 250' Spool	Nickel
* 16564	Sold by Foot or 250' Spool	Brass

**Beaded Chain with Connector**  
.011 Gauge 1/8" Diameter Ball 75 Balls per Foot

Item No.	Length	Finish
70168	5 Ft.	Brass
77012	1 Ft.	Solid Brass
77050	3 Ft.	Solid Brass
77043	12 Ft.	Solid Brass
77064	3 Ft.	Antique Brass
77109	12 Ft.	Antique Brass
77051	3 Ft.	White Plastic
77054	3 Ft.	Oil Rubbed Bronze
77049	3 Ft.	Stainless Steel
77238	3 Ft.	Brushed Nickel
77063	3 Ft.	Chrome
77107	12 Ft.	Chrome


**70662**  
\* 16584  
3' White Braided Cord  
Nickel Finish Connector and End Bell Attached



70168




77012  
77050  
77043




77238




77049




77063  
77107



77051



77054



77064  
77109

CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# CANOPY KITS

## Modern Canopy Kits with Center Hole

5" Diameter  
 7/16" Center Hole  
 40 lb. Load Rating

Includes:

- 1 Canopy
- 1 Screw Collar Loop
- 2 Mounting Screws
- 1 Lock Washer
- 1 Locknut



**70035**  
 Antique Brass Finish



**70037**  
 White Finish



**70033**  
 Brushed Nickel Finish



**70059**  
 Brushed Pewter Finish



**70036**  
 Black Finish



**70038**  
 Oil Rubbed Bronze Finish

## Traditional Canopy Kits with Center Hole

5 1/8" Diameter  
 7/16" Center Hole  
 50 lb. Load Rating

Includes:

- 1 Canopy
- 1 Crossbar
- 4 Mounting Screws
- 1 Lock Washer
- 1 Locknut
- 1 Screw Collar Loop
- 2 Cap Nuts



**70053**  
 Antique Brass Finish



**70050**  
 Oil Rubbed Bronze Finish



**70048**  
 Brushed Nickel Finish



**70052**  
 Brass Finish



**70054**  
 Brushed Pewter Finish



**70055**  
 Black Finish



**70056**  
 White Finish

\*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY.

[www.westinghouselighting.com](http://www.westinghouselighting.com)

# CANOPIES & BLANK-UP KITS



**\* 18134**  
**Canopy Extension Collar**  
 White Finish  
 Gives Canopy 1½" Additional Depth  
 Depth - 1½"  
 Diameter - 5¾"



**70049**  
**Canopy**  
 Antique Brass Finish  
 Diameter - 5"  
 1⅛" Center Hole  
 (Use with Screw Collar Loop Kit, Item# 70352 on page 200)



†29453 - Holes Spaced 2¾" Apart  
 70064 - Holes Spaced 2¾" Apart  
 Mounts on 3" or 4" Outlet Box

†29452 - Holes Spaced 3½" Apart  
 70065 - Holes Spaced 3½" Apart  
 Mounts on 4" Outlet Box

**White Outlet Concealer**  
 Diameter - 4¾"

Includes:  
 • 2 8-32 x ¾" White Head Screws

†Polybagged Bulk Items



**70045**  
**Ceiling Blank-Up Kit**  
 White Finish  
 Diameter - 5"  
 7/16" Center Hole

Includes:  
 • 1 Canopy  
 • 1 ½-IP x 2½" Nipple  
 • 1 ¾-IP x ½-IP Reducing Bushing  
 • 1 Cap Nut



**70058**  
**Blank-Up Kit**  
 White Finish  
 Diameter - 5"  
 Holes Spaced 2¾" Apart

Includes:  
 • 1 Canopy  
 • 1 Crossbar  
 • 2 Mounting Screws  
 • 2 Cap Nuts

CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# SWAG LIGHT KITS & CHAIN



### Swag Light Kits

- Includes:
- 11 Gauge Chain
  - SPT-1 Cord Set
  - Cord Switch
  - 2 Swag Hooks
  - Mounting Hardware
  - 35 lb. Load Rating
- Complete installation instructions included.*



70470 - 15 Ft. Chain,  
20 Ft. Cord  
70480 - 12 Ft. Chain,  
15 Ft. Cord  
**Polished Brass Finish**  
*Gold Cord with White Switch*



70471 - 15 Ft. Chain,  
20 Ft. Cord  
70481 - 12 Ft. Chain,  
15 Ft. Cord  
**Antique Brass Finish**  
*Opaque Gold Cord with Brown Switch*



70530 - 15 Ft. Chain,  
20 Ft. Cord  
70531 - 12 Ft. Chain,  
15 Ft. Cord  
**White Finish**  
*White Cord with White Switch*

Swag Kit Contents Listed Above



### Swag Light Kits

- Includes:
- 11 Gauge Chain
  - SPT-2 Cord Set
  - White Cord Switch
  - 2 Swag Hooks
  - Mounting Hardware
  - 35 lb. Load Rating
- Complete installation instructions included.*



77002 - 18 Ft. Chain,  
20 Ft. Cord  
**Antique Brass Finish**



70125 - 18 Ft. Chain,  
20 Ft. Cord  
**Oil Rubbed Bronze Finish**



70126 - 18 Ft. Chain,  
20 Ft. Cord  
**Brushed Nickel Finish**



77003 - 18 Ft. Chain,  
20 Ft. Cord  
**White Finish**

Swag Kit Contents Listed Above



70070



70071



70072



70074



70075



70079



70670

### 3 Ft. 11 Gauge Fixture Chains, 35 lb. Load Rating

- 70070 - Polished Brass Finish
- 70071 - Antique Brass Finish
- 70072 - Flat Black Finish
- 70074 - Oil Rubbed Bronze Finish

- 70075 - Brushed Nickel Finish
- 70079 - Rust Finish
- 70670 - White Finish

### 8 Gauge Fixture Chains, 50 lb. Load Rating, Sold by the Yard

- \* 21461 - Chrome Finish
- \* 21457 - Flat Black Finish

\*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY.



# SWAG HOOK KITS



70440



70441



70442



70443



70446

### Large 2½" Swag Hook Kits

- 70440 - Polished Brass Finish
- 70441 - Antique Brass Finish
- 70442 - Black Finish
- 70443 - White Finish
- 70446 - Brushed Pewter Finish

### Includes:

- 1 Hook
- 1 Spring Toggle Wing
- 1 Running Thread Stud: ¼-20 x 2½"
- 1 Wood Screw: #14 x 1½"
- 45 lb. Load Rating



70444



70450



70451



70452



70453



70454



70770

### 1½" Swag Hook Kits

- 70444 - Brushed Pewter Finish
- 70450 - Polished Brass Finish
- 70451 - Antique Brass Finish
- 70452 - Black Finish
- 70453 - Antique Copper Finish
- 70454 - Oil Rubbed Bronze Finish
- 70770 - White Finish

### Includes:

- 2 Hooks
- 2 Spring Toggle Wings
- 2 Running Thread Studs: #10-24 x 2⅞"
- 2 Wood Screws: #10 x 1¼"
- 30 lb. Load Rating

### 70447

#### 2½" Swag Hook Kit

### Includes:

- 1 Brushed Nickel Finish Swag Hook
- 1 Oil Rubbed Bronze Finish Swag Hook
- 2 Spring Toggle Wings
- 2 Running Thread Studs: ¼-20 x 2⅞"
- 2 Wood Screws: #14 x 1½"
- 45 lb. Load Rating



### \* 69559 70099

#### Fixture Chain Pliers

7" Long

Used for Easy Opening  
and Closing of Chain Links  
Works with up to 3 Gauge Chain



CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# MAKE-A-LAMP KITS

All Make-A-Lamp Kits include SPT-1 cord.



**70025**  
**Electrified Candlestick and Bottle Adapter**

- Includes:
- 8' 18 Gauge Cord Set
  - Push-Through Medium Base Socket
  - 150 Watts Max. Rating
  - 3 Rubber Bottle Adapters
  - Hardware



**70455**  
**Make-A-Lamp 3-Way Socket Kit**  
*Brushed Nickel Finish*

- Includes:
- 10" Detachable Harp
  - 8' 18 Gauge Cord Set
  - 3-Way Medium Base Socket
  - 150 Watts Max. Rating
  - Finial
  - Hardware



**70268**  
**Make-A-Lamp 3-Way Socket Kit**  
*Polished Brass Finish*

- Includes:
- 10" Detachable Harp
  - 8' 18 Gauge Cord Set
  - 3-Way Medium Base Socket
  - 150 Watts Max. Rating
  - Finial
  - Hardware



**70269**  
**Make-A-Lamp Push-Through Socket Kit**  
*Polished Brass Finish*

- Includes:
- 10" Detachable Harp
  - 8' 18 Gauge Cord Set
  - Push-Through Medium Base Socket
  - 150 Watts Max. Rating
  - Finial
  - Hardware



**70266**  
**Make-A-Lamp Electric Bottle Adapter Kit**  
*Polished Brass Finish*

- Includes:
- 10" Detachable Harp
  - 8' 18 Gauge Cord Set
  - Push-Through Medium Base Socket
  - 150 Watts Max. Rating
  - Finial
  - 3 Rubber Bottle Adapters
  - Hardware


CARDED PRODUCT SOLD IN INNER PACK ONLY.

# HARPS

**\* 19106**  
**9" Two-Piece Heavy-Duty Detachable Harp**  
*Polished Brass Finish*



**70225**  
**Adjustable Detachable Harp**  
*Brushed Nickel Finish*  
 Height Adjusts to 8½", 9½", or 10½"



**70218 - 6½"**  
**70220 - 8"**  
**70221 - 9"**  
**70222 - 10"**  
**70224 - 12"**  
**Two-Piece Detachable Harp**  
*Polished Brass Finish*



**70226 - 8"**  
**70227 - 10"**  
**Two-Piece Detachable Harp**  
*Brushed Pewter Finish*



**70689 - 8"**  
**70690 - 10"**  
**Two-Piece Detachable Harp**  
*Rustic Bronze Finish*



**\* 19066 - 7"**  
**\* 19068 - 8"**  
**\* 19070 - 9"**  
**\* 19072 - 10"**  
**Two-Piece Detachable Harp**  
*Polished Brass Finish*



**70219**  
**Clip-On Lamp Adapter**  
*Clips Onto Medium Base A Shape Lamps*  
*Brass Finish*  
 Threaded ¼-27  
 Height - 3 1/16"  
 Width - 2 1/8"  
 Depth - 1/2"  
 Overall Height - 4"

CARDED PRODUCT SOLD IN INNER PACK ONLY.

**\*Bulk Pack**

# FINIALS & KNOBS



**70166**  
**Clear Glass Ball**  
**Lamp Finial**  
 Brushed Nickel Finish  
 Height - 1¾"  
 Tapped ¼-27



**70165**  
**Modern Acorn**  
**Lamp Finial**  
 Oil Rubbed Bronze  
 Height - 1¾"  
 Tapped ¼-27



**70164**  
**Modern Acorn**  
**Lamp Finial**  
 Brushed Nickel Finish  
 Height - 1¾"  
 Tapped ¼-27



**70133**  
**Acorn Knob**  
**Lamp Finial**  
 Brass Finish  
 Height - 1½"  
 Tapped ¼-27  
 Finial Thread Reducer  
 Tapped ⅛-M to ¼-27-F



**70141**  
**Acorn Knob**  
**Lamp Finial**  
 Nickel Finish  
 Height - 1½"  
 Tapped ¼-27  
 Finial Thread Reducer  
 Tapped ⅛-M to ¼-27-F



**70321**  
**Victorian**  
**Lamp Finial**  
 Tiffany Antique  
 Brass Finish  
 Height - 1¼"  
 Tapped ¼-27



**70004**  
**Semi Ornate Floral**  
**Lamp Finial**  
 Oil Rubbed  
 Bronze Finish  
 Height - 1½"  
 Tapped ¼-27



**70005**  
**Classic Ball**  
**Lamp Finial**  
 Oil Rubbed  
 Bronze Finish  
 Height - 1½"  
 Tapped ¼-27



**70006**  
**Classic Ball**  
**Lamp Finial**  
 Brushed  
 Nickel Finish  
 Height - 1½"  
 Tapped ¼-27

CARDED PRODUCT SOLD IN INNER PACK ONLY.





**70131 (Carded 2-Pack)**  
**Two Lamp Knobs**  
 Brass Finish  
 Height - 1¼"  
 Tapped ¼-27



**70138 (Carded 2-Pack)**  
**Two Lamp Knobs**  
 Nickel Finish  
 Height - 1¼"  
 Tapped ¼-27



**70130 (Carded 2-Pack)**  
**Two Lamp Finials**  
 Solid Brass  
 Height - 2"  
 Tapped ¼-27



**70135**  
**Lamp Finial**  
 Solid Brass  
 Height - 2"  
 Tapped ¼-27



**\*10649**  
**70676**  
**Lamp Finial**  
 Aged Iron Finish  
 Height - 2"  
 Tapped ¼-27



**\* 16356**  
**70136 (Carded 2-Pack)**  
**Lamp Finial**  
 Brass Finish  
 Height - 1"  
 Tapped ¼-27



**70144**  
**(Carded 2-Pack)**  
**Two Lamp Finials**  
 Nickel Finish  
 Height - 1"  
 Tapped ¼-27



CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# PARTS & ACCESSORIES



**77270**  
**48" Down Rod**  
**Wire Extension Kit**  
 4 Wires with  
 4 Connectors



**\* 21494**  
**Bare Copper Ground**  
**Wire With Lug**  
 18 Gauge  
 Slips 8/32 Thread  
 9" Lead



**70641**  
**10' Copper**  
**Ground Wire**  
 18 Gauge



**70506 - Brown Finish**  
**70500 - White Finish**  
**Feed-Through**  
**On/Off Switch**  
 For Use with No. 18,  
 SPT-1 Wire Only  
 3A



**Cord Sets**  
 18/2 SPT-1, 105° Wire  
**Transparent Silver**  
**\* 23055 - 15'**  
**Transparent Gold**  
**\* 23033 - 8'**  
**\* 23053 - 15'**



**Cord Sets**  
 18/2 SPT-1, 105° Wire  
**Black**  
**\* 23032 - 8'**  
**\* 23052 - 15'**  
**White**  
**\* 23030 - 8'**  
**\* 23050 - 15'**  
**Brown**  
**\* 23031 - 8'**  
**\* 23051 - 15'**



**70098**  
**8' Silver Cord Set**  
 Polarized Plug  
 18-2 SPT-2, 105° Wire



**70100**  
**8' White Cord Set**  
 Polarized Plug  
 18-2 SPT-1, 105° Wire



**70101**  
**8' Brown Cord Set**  
 Polarized Plug  
 18-2 SPT-1, 105° Wire



**70105**  
**8' Gold Cord Set**  
 Polarized Plug  
 18-2 SPT-1, 105° Wire



**70103**  
**15' Gold Cord Set**  
 Polarized Plug  
 18-2 SPT-1, 105° Wire

On All Cord Sets Free Ends are Split, Stripped and Tipped



Great for Seasonal Ceramics and Crafts

- \*23305 - 6' White
  - 70108 - 6' White
  - \*23306 - 6' Brown
  - 70003 - 6' Brown
- Cord Set with Snap-In Pigtail Candelabra Base Socket and Cord Switch**  
 No. 18-2, SPT-1, 105° Wire  
 75 Watts, 125 Volts  
 Snap-In Spring Fits 1" Hole  
 Switch is 12" from Socket




- \*23302 - 8' White
  - \*23303 - 8' Brown
- Cord Set With Switch Cat Tipped**  
 No. 18-2, SPT-1, 105°  
 Wire Switch is 12" from End



- \*23311 - 6' White
- Cord Set With Snap-In Pigtail Candelabra Base Socket**  
 No. 18-2, SPT-1, 105° Wire  
 75 Watts  
 125 Volts  
 Snap-In Spring Fits 1" Hole



- 70801
- Halogen Dimmer For Torchiere Lamps**  
 Includes Knob  
 500 Watt Maximum, 120 VAC



CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# PLUGS



\* 22600 - Brown  
 \* 22601 - Ivory  
**Polarized Plug**  
 SPT-1 Wire, Side Entry  
 Easy -Connect



\* 22631 - Brown  
 \* 22632 - White  
**Polarized Plug**  
 SPT-1 Wire, Top Entry



\* 22633  
**Heavy Duty Outdoor 3-Prong Plug**  
 Plastic Cord Clamp  
 1/16" Hole  
 15A, 125 Volts  
 Cord Grip Range 245-700"  
 12 thm, 18 AWG



\* 22635  
**Heavy Duty Outdoor Female Connector**  
 Plastic Cord Clamp  
 3/8" Hole  
 15A, 125 Volts



74321  
**Eight Clear Safety Caps**  
 Covers Outlets



\* 22532  
**Snap-In Outlet with Ground Wire**  
 Black  
 6" Wire Leads  
 14 Gauge  
 15A, 125 Volts  
 Fits 1" Square Opening  
 with Green Ground Wire  
 Height - 7/8"



# ACCESSORIES



- \* 24105 - 3" Long
- \* 24109 - 4" Long
- 70370 - 4" Long (Carded 2-Pack)
- \* 24115 - 6" Long
- White Plastic  
Candle Socket Cover**
- Candelabra Base
- I.D. -  $2\frac{5}{32}$ "
- O.D. -  $\frac{7}{8}$ "



- \* 24140 - 4" Long White
- 70371 - 4" Long White (Carded 2-Pack)
- 70374 - 4" Long Ivory (Carded 2-Pack)
- \* 24147 - 6" Long White
- Plastic Candle  
Socket Cover**
- Medium Base
- I.D. -  $1\frac{5}{32}$ "
- O.D. -  $\frac{1}{4}$ "



- \* 24059
- 70373 (Carded 2-Pack)
- Ivory Plastic  
Candle Socket Cover**
- Candelabra Base
- 4" Long
- I.D. -  $2\frac{5}{32}$ "
- O.D. -  $\frac{7}{8}$ "



- 70368
- Two 4" Plastic  
Candle Socket Covers**
- Tan Drip
- Candelabra Base
- I.D. -  $\frac{3}{4}$ "
- O.D. -  $1\frac{1}{16}$ "



- 70300
- Five 1½"  
Crystal Prisms**
- Clear

- 74998 - Single Gang
- 74999 - Double Gang
- Plastic Wall Shield**




CARDED PRODUCT SOLD IN INNER PACK ONLY.

\*Bulk Pack

# ACCESSORIES

**70900 - White Finish**  
**40" Wire Cover**  
 Can be painted or stained  
 Use latex stain only



**41298 - 16 oz.**  
**41299 - 32 oz.**  
**Extend-A-Finish**  
**Crystal and Fixture**  
**Cleaner**

- Features:
- Will Not Streak or Spot
  - Drip Dry
  - No Ammonia
  - Will Not Harm Metal Framework or Finish



**70298**  
**Extend-A-Finish**  
**Crystal and Fixture**  
**Cleaner**  
 Box contains 6 bottles  
 of Item #41298



**77000**  
**Chenille Microfiber**  
**Adjustable Brush Duster**  
**with Telescopic Pole**

- Extends to 62" and adjusts to any angle.
- Telescopic handle and adjustable head for cleaning hard-to-reach items.
- Attracts and holds dust.
- Cleans without using sprays or chemicals.
- Hand washable.



**77105**  
**All Purpose**  
**Electrostatic Duster**

- Telescopic handle extends up to 72".
- Flexible head adjusts to any angle.
- Perfect for cleaning fan blades, fixtures or any other hard-to-reach household items.



Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
01010	161	18134	207	22282	194	23302	215
01011	73, 157	19066	211	22303	198	23303	215
0101108	81, 157	19068	211	22306	198	23305	215
01020	165	19070	211	22310	198	23306	215
0102011	165	19072	211	22320	198	23311	215
01020DISP	165	19106	211	22321	198	24059	217
01030	167	21003	200	22324	198	24105	217
0103011	167	21004	201	22370	154, 193	24109	217
01036	167	21005	201	22371	193	24115	217
0103611	167	21006	201	22372	194	24140	217
01036DISP	167	21008	201	22377	190	24147	217
0104011	165	21030	201	22380	190	29452	207
01050	165	21032	200	22381	190	29453	207
0105011	165	21036	201	22382	190	41298	218
01050DISP	165	21038	201	22402	195	41299	218
0105211	165	21457	208	22403	195	60004	67
01070	169	21461	208	22406	195	61006	66
01100	162	21494	214	22411	195	61007	65
01240	166	21530	204	22451	197	61008	65
0124011	166	22000	196	22452	197	61009	67
01240DISP	166	22001	191	22453	197	61011	67
01250	166	22003	191	22454	197	61012	67
0125011	166	22011	191	22456	197	61013	67
01400	163	22031	191	22457	197	61017	69
01525	164	22041	191	22458	197	61019	69
0152511	164	22051	191	22470	196	61024	73
01525DISP	164	22125	192	22471	196	61026	65
0200011	168	22126	192	22472	196	61030	72
0252511	168	22127	192	22480	196	61031	70
02525DISP	168	22136	192	22481	196	61032	70
09842	81	22138	192	22490	197	62034	83
09843	95	22150	194	22491	197	62038	87
09844	85	22200	190	22501	189	62039	87
10649	213	22205	189	22502	189	62040	88
11104	196	22207	189	22503	189	62041	84
11107	196	22212	193	22504	189	62042	88
11108	196	22213	190	22505	189	62043	87
11110	196	22214	190	22532	216	62044	87
11744	203	22215	190	22551	192	62045	87
12055	203	22216	190	22560	197	62046	83
12060	203	22217	190	22561	197	62047	84
13204	202	22218	194	22562	197	62048	87
13206	202	22220	190	22600	216	62049	13, 43
13212	202	22222	190	22601	216	62050	13, 43
13216	202	22223	190	22631	216	62051	66
13224	202	22234	189	22632	216	62052	66
13232	202	22237	189	22633	216	62053	66
13248	202	22256	188	22635	216	62054	66
13312	202	22259	188	23030	214	62201	68
13352	202	22266	194	23031	214	62224	58
13650	202	22267	195	23032	214	62235	31, 58
16356	213	22269	195	23033	214	62238	31, 52
16564	154, 205	22272	193	23050	214	62239	31, 52
16565	154, 205	22273	194	23051	214	62257	30, 35
16572	154, 205	22274	195	23052	214	62259	30, 35
16576	154, 205	22276	194	23053	214	62260	30, 52
16584	205	22281	194	23055	214	62274	30, 59

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
62275	30, 59	63061	26, 68	63183	83	63436A	22, 59
62278	30, 52	63062	26, 36	63215	86	63436B	22, 59
62279	30, 52	63065	26, 35	63216	13	63437A	22, 50
62301	88	63066	26, 49	63217	13	63437B	22, 50
62303	89	63068	26, 49	63218	11, 33	63438A	20, 48
62306	88	63069	26, 49	63219	11, 33	63438B	20, 48
62307	89	63070	26, 49	63220	11, 33	63438C	20, 48
62309	90	63071	17, 57	63221	11, 33	63441A	20, 56
63000	75	63072	18, 57	63222	11, 33	63441B	20, 56
63001	29, 59	63073	18, 47	63223	11, 33	63441C	20, 56
63002	75	63074	18, 47	63224	11, 33	63442A	21, 47
63003	75	63075	18, 47	63225	11, 33	63442B	21, 47
63004	29, 69	63076	9, 45	63226	11, 33	63442C	21, 47
63005	75	63077	9, 45	63227	11, 33	63443A	21, 57
63006	75	63079	9, 63	63228	11, 33	63443B	21, 57
63007	29, 68	63080	18, 56	63229	11, 33	63443C	21, 57
63008	75	63081	18, 45	63230	11, 33	63444	37
63009	75	63082A	10, 62	63231	11, 33	63445	37
63012	74	63082B	10, 62	63232	11, 33	63446	37
63013	74	63083A	10, 62	63233	11, 33	63447	15, 63
63015	29, 51	63083B	10, 62	• 63234	83	63448	15, 46
63019	29, 51	63084A	10, 62	• 63235	66	63449	15, 46
63020	29, 51	63084B	10, 62	• 63236	66	63450	15, 55
63021	17, 46	63085A	10, 62	63400	25, 36	63451	67
63022	17, 46	63085B	10, 62	63401	25, 50	63452	67
63023	17, 36	63086A	10, 62	63402	25, 68	63453	67
63024	19, 56	63086B	10, 62	63403	25, 35, 61	63454	67
63025	18, 45	63087A	10, 62	63404	25, 58	63455	63
63026	18, 45	63087B	10, 62	63405	25, 36	63456	63
63027	24, 49	63088	12, 34	63406	25, 50	63457	65
63028	24, 49	63089	12, 34	63407	25, 58	63458	65
63029	24, 55	63090	63	63408	21, 37	63459	66
63030	18, 36	63091	65	63409	23, 37	63460	64
63031	16, 60	63092	65	63410	23, 37	63461	64
63033	16, 60	63093	65	63412	23, 56	63462	64
63034	24, 50	63095	65	63413	23, 36	63463	64
63035	24, 50	63096	63	63414	23, 36	63464	64
63036	24, 50	63099	63	63415	23, 47	63465	64
63037	16, 60	63119	9, 45	63416	31, 35	63466	64
63038	16, 60	63120	83	63417	31, 35, 61	64000	85
63039	19, 48	63123	86	63418	16, 60	64001	84
63040	19, 48	63124	86	63419	16, 60	64002	85
63041	19, 48	63125	86	63420	17, 55	64003	85
63042	28, 59	63126	86	63421	17, 46	64004	85
63043	28, 69	63131	88	63422	17, 37	64005	12, 34
63044	28, 61	63134	88	63423	37	64006	12, 34
63047	28, 68	63135	88	63424	36	64007	12, 34
63048	28, 35	63137	89	63425	37	64008	12, 34
63049	28, 51	63142	89	63426	36	64009	12, 34
63051	28, 51	63143	89	63427	22, 37	64010	9, 63
63052	28, 51	63148	87	63428	19, 49	64011	13, 43
63054	29, 61	63150	86	63429	19, 57	64012	12, 34
63056	29, 35	63155	83	63431	19, 68	64290	39
63057	27, 58	63156	84	63432	19, 36	64291	39
63058	27, 61	63157	84	63433	15, 55	64292	39
63059	27, 61	63181	86	63434	15, 46	64300	38
63060	27, 61	63182	86	63435	15, 46	64301	38

• *New Item*



Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
64302	38	66658	41	67835	94	70115	200
64303	38	66680	41	67836	94	70125	208
64304	38	66686	41	67901	94	70126	208
64305	38	66689	40	67930	92	70130	213
64306	38	66692	41	67973	94	70131	213
64316	38	66699	40	67975	94	70133	212
64340	39	66741	89	67978	95	70135	213
64360	39	66742	89	69231	68	70136	213
64617	31, 52	66746	89	69407	90	70138	213
64684	92	66800	93	69559	209	70141	212
64688	91	66803	95	69919	92	70144	213
64689	91	66808	94	70000	195	70145	189
64829	92	66818	93	70001	195	70146	189
64841	88	66822	96	70003	215	70150	202
64883	92	66823	96	70004	212	70151	202
66162	38	66840	95	70005	212	70152	203
66198	69	66853	91	70006	212	70153	203
66200	43	66859	96	70010	193	70155	203
66201	43	66861	95	70025	210	70156	204
66203	42	66875	96	70031	148	70158	204
66204	42	66878	93	70032	148	70159	204
66206	43	66879	94	70033	206	70160	192
66214	41	66881	94	70035	206	70161	192
66223	35	66882	93	70036	206	70162	203
66238	42	66884	93	70037	206	70164	212
66239	42	66885	93	70038	206	70165	212
66240	42	66898	92	70045	207	70166	212
66241	42	66919	93	70048	206	70168	154, 205
66242	43	66924	91	70049	207	70169	204
66263	43	66946	96	70050	206	70172	203
66282	39	66949	93	70052	206	70176	202
66297	43	66955	94	70053	206	70218	211
66326	41	66961	91	70054	206	70219	211
66327	38	66964	91	70055	206	70220	211
66401	53	66970	91	70056	206	70221	211
66402	52	66971	92	70058	207	70222	211
66403	53	66972	92	70059	206	70224	211
66406	53	66975	96	70064	207	70225	211
66411	53	66976	96	70065	207	70226	211
66414	53	66983	91	70070	208	70227	211
66424	53	66991	94	70071	208	70230	188
66448	53	67202	40	70072	208	70231	188
66449	53	67208	41	70074	208	70234	188
66450	53	67209	40	70075	208	70236	188
66496	31, 52	67210	40	70079	208	70238	188
66497	31, 52	67215	40	70098	214	70242	188
66522	51	67328	92	70099	209	70243	188
66523	51	67345	42	70100	214	70250	204
66594	53	67384	69	70101	214	70254	204
66595	53	67480	74	70103	214	70255	204
66601	52	67482	74	70105	214	70256	204
66607	41	67485	74	70108	215	70258	204
66609	40	67514	52	70110	200	70266	210
66610	40	67572	39	70111	200	70268	210
66611	40	67573	39	70112	200	70269	210
66624	41	67831	90	70113	200	70270	202
66654	52	67834	90	70114	201	70272	202

• *New Item*

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
70284	73	70500	214	• 72051	108	75050	97
70285	73	70506	214	• 72053	108	75051	97
70286	73	70530	208	• 72059	106	75052	97
70287	73	70531	208	• 72065	111	75053	97
70290	199	70601	202	• 72074	105	77000	152, 218
70298	218	70602	202	• 72076	123	77002	208
70300	217	70603	202	• 72077	104	77003	208
70321	212	70604	202	• 72078	104	77004	152
70350	200	70606	202	• 72079	127	77005	152
70352	200	70613	202	• 72089	110	77006	152
70361	195	70620	203	• 72090	108	77007	151
70364	194	70621	203	• 72091	106	77008	151
70368	217	70622	203	• 72092	118	77009	151
70370	217	70628	203	• 72094	124	77012	154, 205
70371	217	70630	203	• 72096	129	77013	151
70373	217	70632	204	• 72097	129	77014	151
70374	217	70633	204	• 72098	138	77015	154
70402	192	70634	204	• 72128	132	77016	154, 204
70403	192	70635	204	• 72130	132	77019	151
70406	191	70636	204	• 72131	130	77021	155, 199
70407	189	70638	203	• 72132	130	77022	155, 199
70408	193	70639	203	• 72133	135	77023	155, 199
70409	193	70640	204	• 72135	135	77027	160
70410	191	70641	214	• 72136	134	77028	160
70411	191	70660	203	• 72138	134	77029	151
70412	191	70661	151, 205	72141	113	77030	151
70413	191	70662	205	• 72144	134	77034	160
70415	191	70663	203	• 72149	133	77035	160
70417	191	70670	208	• 72150	133	77036	151
70419	193	70676	213	• 72151	133	77037	160
70421	191	70689	211	• 72157	133	77040	154, 204
70424	193	70690	211	• 72158	135	77041	154, 204
70425	193	70770	209	• 72159	132	77043	154, 205
70426	193	70801	215	• 72160	131	77044	154, 205
70428	195	70900	218	72161	113	77045	154, 205
70429	193	72000	125	• 72162	130	77046	154, 205
70430	189	72005	124	• 72163	131	77047	154, 204
70431	191	72006	124	• 72164	131	77048	154, 204
70433	189	72007	139	• 72165	131	77049	154, 205
70435	195	72008	139	72229	121	77050	154, 205
70440	209	72011	107	72243	121	77051	154, 205
70441	209	72014	128	72245	120	77052	155, 199
70442	209	72016	112	72261	118	77054	154, 205
70443	209	72017	110	7226565	117	77058	154
70444	209	72019	109	7234265	117	77059	154
70446	209	72020	141	72471	121	77060	153
70447	209	72021	141	72472	120	77061	153
70450	209	72032	129	72473	109	77063	154, 205
70451	209	72036	123	72474	114	77064	154, 205
70452	209	72037	123	72475	118	77066	154, 205
70453	209	• 72039	103	72477	106	77069	151
70454	209	72040	105	72557	111	77072	151
70455	210	72041	109	72559	117	77073	155, 199
70470	208	• 72042	103	72598	114	77075	155, 199
70471	208	72043	137	74321	216	77077	154, 193
70480	208	72044	111	74998	217	77079	153
70481	208	• 72046	105	74999	217	77083	151

• *New Item*

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
77084	152	77402	153	78127	142	81121	80, 177
77087	151	77403	153	7813665	107	81151	184
77088	152	77405	153	7814465	119	81160	179
77091	155, 199	77406	153	7814565	119	81162	179
77093	152	77407	153	7824865	119	81167	79, 176
77095	152	77408	153	7839165	126	81169	179
77096	152	77409	153	78399	125	81208	176
77103	150	77410	153	78400	125	81227	80, 177
77104	152	77411	153	78409	142	81230	184
77105	152, 218	77413	153	7843565	128	81242	178
77107	154, 205	77414	153	78505	116	81253	80, 177
77108	150	77415	153	78507	116	81254	182
77109	154, 205	77416	153	7852165	126	81257	79, 177
77118	150	77417	153	78524	113	81258	177
77121	152	77491	148	7856865	126	81265	79, 176
77122	150	77492	148	78614	141	81270	80, 178
77125	150	77526	148	7861965	139	81272	79, 176
• 77126	150	77527	148	7862765	127	81275	176
• 77129	150	77528	148	78631	121	81277	79, 176
• 77132	150	77620	150	78644	121	81279	79, 176
77134	152	77621	150	7867865	127	81282	178
• 77135	150	77640	150	78691	115	81290	181
77214	150	77642	150	78763	120	81310	77, 174
77215	150	77732	160	78764	109	81311	77, 174
77217	152	77733	160	7877365	128	81314	79, 175
77218	152	77750	159	78775	115	81315	79, 175
77220	151	77752	159	7877865	138	81333	80, 178
77224	151	77754	159	81000	25, 76, 171	81353	79, 176
77225	151	77756	159	81002	25, 76, 171	81355	178
77238	154, 205	77757	159	81003	23, 77, 174	81356	80, 177
77240	148	77762	159	81004	23, 77, 174	81363	79, 176
77241	148	77764	159	81005	19, 78, 175	81364	78, 175
77243	148	• 77844	147	81006	22, 76, 171	81365	80, 178
77244	148	• 77845	147	81009	18, 21, 76, 171	81382	80, 178
77246	148	• 77846	147	81013	22, 76, 171	81391	79, 176
77249	148	• 77847	147	81014	20, 76, 171	81400	77, 174
77251	148	• 77848	147	81015	21, 76, 171	81404	77, 174
77252	148	• 77849	147	81016	20, 76, 171	81405	78, 175
77254	148	• 77850	147	81017	17, 21, 76, 171	81407	77, 174
77257	148	• 77851	147	81018	20, 77, 174	81409	77, 174
77258	148	• 77852	147	81019	71, 173	81410	78, 175
77259	148	• 77853	147	81020	71, 172	81412	78, 175
77265	148	77870	149	81021	71, 172	81413	78, 175
77268	153	77871	149	81022	70, 172	81414	78, 177
77269	154	77872	149	81023	71, 173	81422	79, 176
77270	155, 214	77873	149	81024	70, 172	81427	78, 175
77285	155, 199	77874	149	81025	70, 172	81450	183
77286	155, 199	77875	149	81051	80, 177	81452	184
77287	155, 199	78000	137	81066	177	81457	184
77288	155, 199	78001	110	81082	178	81459	184
77289	152	78002	103	81094	177	81479	177
77290	151	78003	141	81095	79, 176	81493	185
77291	151	7801665	107	81097	80, 178	81494	185
77292	151	7801765	107	81098	79, 176	81499	185
77293	152	78024	142	81100	184	81501	182
77400	153	7804365	127	81119	79, 176	81514	185
77401	153	78053	134	81120	80, 178	81528	181

• *New Item*

Item#	Page#	Item#	Page#
81549	182	85005	77, 174
81560	182	85006	18, 76, 171
81570	182	85012	77, 174
81571	182	85031	71, 173
81574	182	85033	71, 173
81575	182	85036	71, 173
81578	181	85038	71, 173
81592	181	85043	28, 29, 76, 171
81609	181	85044	19, 76, 171
81613	181	85045	19, 76, 171
81620	181	85046	27, 77, 174
81720	180	85047	24, 76, 171
81727	180	• 85050	78, 175
81758	184	• 85051	71, 173
81759	184	• 85052	71, 173
81760	184	85100	184
81764	184	85151	184
81770	180	85162	179
81800	180	85254	182
81805	180	85282	178
81807	180	85338	182
81810	180	85450	183
81819	180	85528	181
81837	180	85570	182
81869	183	85571	182
81876	184	85578	181
81877	183	85602	182
81883	183	85604	184
81884	183	85606	181
81887	183	85608	181
81900	183	85612	182
81901	183	85613	181
81905	183	85617	184
81918	183	85701	77, 174
81919	183	85702	77, 174
81925	180	85705	182
83062	179	85707	182
83063	179	85712	182
83070	179	85718	73
83071	179	85722	78, 175
83072	179	85724	78, 175
83090	179	85730	78, 175
83091	179	85757	181
83100	179	85869	183
83101	179		
83102	179		
83757	181		
• 85003	77, 174		
• 85004	76, 171		

• *New Item*







**Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com).**

©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.