



ELK

ELK
LIGHTING CREATIVITY™

CATALOG 3006



CATALOG 3006

The image features three glass pendant light fixtures against a dark background. Each fixture contains a glowing Edison-style filament bulb. The leftmost fixture has a glass shade with a subtle, irregular texture. The middle fixture has a smooth, clear glass shade. The rightmost fixture has a glass shade with a prominent, raised, pebbled texture. The text 'SAFEGUARDING TRADITION' is positioned over the left fixture, and 'CHALLENGING CONVENTION' is positioned over the right fixture.

SAFEGUARDING TRADITION CHALLENGING CONVENTION

COLLABORATION

Working in unison, our design team incorporates the latest "next-trend" materials and techniques across our complete line of lighting, furniture, art, and accessory brands. Together, these creative threads form an array of complimentary home furnishing options.



TRADITION

For more than 30 years, discerning customers have known the ELK name to be synonymous with a commitment to transcend the boundaries of innovation and style while offering artful lighting and décor products.



THE UBIQUITY OF NATURE'S
INSPIRATION FUELS OUR MINDS
AND CAPTIVATES OUR HEART


COMMUNITY

The foundation of our social responsibility programs is ingrained in the ideal that the support given today benefits the generations of tomorrow. We provide aid to organizations such as Habitat for Humanity, Concourse for Kids, the Embrace Kids Foundation, and many local community programs. We also fight global deforestation through a semi-annual tree planting initiative and limit the use of natural resources through implementation of the latest energy- saving lighting technologies.



INNOVATION

Our award-winning, international team of designers and engineers brings visionary thinking to the ELK product-development process; we constantly strive to echo themes from the past while creating the styles of the future. In this quest, we uphold a pioneering role in the development of technical and aesthetic aspects that challenge convention.



CRAFTSMANSHIP

From inspiration to design, our curators carefully select quality materials and the appropriate techniques to capture the essential elements of each collection. The character, depth, and richness of the finished pieces reflect the ingenuity and passion of our collective desire to distinguish and define our brand.






RESTORATION
18



CLASSICS
176



TRANSITIONAL
320



MODERN
396



CEILING
484



BATH AND SPA
520



MINI PENDANTS
588



SWINGARMS
646



POCKET SCONCES
658



GAME ROOM
674



NOVELTY
690



OUTDOOR
696



CLICKPLATES
796



MEDALLIONS
800









































































COLLECTIONS

RESTORATION

COLLECTIONS

	Slatington 20		Pesaro 60		Encompass 81		Braxton 104		Brisbane 123		Insulator Glass 136		Schoolhouse Flushes 156		Urban Lodge 169
	Laboratory 22		Perry 62		Park Ridge 82		Diamond Plate 108		Parameters - Nickel 124		Menlow Park 140		Restoration Pendants 157		Early American 170
	Garrett 24		Lewisburg 64		Natural Rope 84		Brendon 109		Parameters - Bronze 125		Yardley 144		Restoration Flushes 158		Chapman 171
	Rutherford 26		Farmhouse 66		Pearce 94		Linden Manor 110		Urbano 126		Danica 146		Norwich 162		Jonas 172
	Carolton 30		Wilmington 72		Alanna 96		Fulton 118		Halophane 128		Bergen 148		Glendora 164		Cog and Chain 174
	Chadwick 34		Delphine 74		Hemispheres 98		Braiden 119		Seaport 130		Watersphere 149		Purcell 165		Vintage Filament Bulbs 175
	Brooksdale 52		Xenia 76		Chesapeake 100		Simpson 120		Warehouse Pendant 132		Hammered Glass 150		Ephrata 166		
	Newberry 56		Hartford 78		Randolph 101		Anza 121		Corrine 133		Quinton Parlor 152		Café 167		
	Palacial 58		Brookline 80		Rialto 102		Murphy 122		Darby 134		Schoolhouse Pendants 154		Strasburg 168		

CLASSICS

	Armand 178		Senecal 206		Cambridge 224		Huarco 248		Jayden 260		Lawrenceville 276		Mix-N-Match Shades 294		Yorkville 310
	Viva Natura 180		Andalusia 208		Emilion 226		Brillaré 250		Aubree 262		Tiffany Buckingham 278		Brimford Rosedale Dragonfly 298		Fenton 311
	Jausten 186		Sasha 210		Allesandria 228		Winterberry 251		Hammond 264		Grapevine 281		Barringer 300		Helene 312
	Empire 188		La Flor 211		Fioritura 229		Rosavita 252		Manning 266		Latham 282		Mica Filigree 302		Lavery 313
	Amherst 190		Rochelle 212		Circeo 230		Opulence 254		Zuela 267		Grape Trellis 284		Mica 304		Decostar 314
	Villegosa 192		Regency 214		Sagemore 236		Elise 256		Chandette 268		Filigree 286		Abington 305		French Damask 315
	Elizabethan 194		Millwood 218		Crystal Branches 238		Princess 257		Veronica 272		Diamond Ring 288		Crystal Spring 306		Preston 316
	Christina 198		Georgian Court 220		Heritage 242		Renee 258		Buckingham 273		English Ivy 290		Chester 308		Linoka 318
	Renaissance 200		Chelsea 222		Cristallo Fiore 244		Donaldson 259		Gloucester 274		Jewelstone 292		Cheltenham 309		Conley 319



TRANSITIONAL

	Morrison 322		Serenity 340		Dione 352		Santa Monica 378
	Delaney 324		Selma 341		Sculptive 354		Cirque 380
	Ventoux 326		Baxter 342		Elysburg 356		Aurora 381
	Madera 328		Clarkton 344		Seven Springs 370		Shells 382
	Jorgenson 330		Dalton 345		Tribeca 371		Luminese 384
	Benicia 332		Pembroke 346		Chandler 372		Glass Mosaic 386
	New York 334		Lilliana 348		Alexis 374		Avalon 388
	Intersections 336		Medford 350		Diffusion 376		Dimensions 390
	Parallax 338		Port Solerno 351		Estonia 377		Spanish Mosaic 391

MODERN

	Links 398		Geoweb 412		Corisande 426
	Crestwood 399		Roxa 413		Refraction 428
	Janette 400		Hammersmith 414		Twilight 432
	Mica 402		Reilly 416		Starburst 434
	Cumberland 405		Lino 418		Zebula 438
	Lindhurst 406		Vasso Chromo 419		Crystal Orbs 440
	Cubist 408		Lindsey 420		Light Spheres 441
	Cubix 410		Chapeau 423		Crystal Sphere 442
	Tetra 411		Sorenson 424		Saturn 443


















MODERN

-  Odyssey 444
-  Optix 456
-  Modern Organics 470
-  Crystoria 445
-  Zoey 458
-  Regis 472
-  Mariana 446
-  Parisienne 460
-  Skyline 473
-  Alea 450
-  Molecular 462
-  Zarah 474
-  Linisfarne 451
-  Winter Forest 464
-  Anastasia 475
-  Crystal Flushmounts 452
-  Viviana 465
-  Medina 476
-  Clearview 453
-  Autumn Breeze 466
-  Woodland Sunrise 478
-  Rados 454
-  Crystals 467
-  Genevieve 480
-  Cortina 455
-  Fabric Cylinders 468
-  Retrovia 482

BATH AND SPA

-  Corrugated Glass 522
-  Talmage 534
-  Optix 543
-  Elysburg 552
-  Encased Crystals 523
-  Briston 535
-  Crystal Wave 544
-  Refraction 556
-  Chiseled Glass 524
-  Retrovia 536
-  Lindale 545
-  Jonas 558
-  Braxton 526
-  Sculptive 537
-  Crystallure 546
-  Retrospectives 559
-  Ventor 528
-  Epsom 538
-  Matrix 547
-  Utica 560
-  Willow Bend 529
-  Linton 539
-  Contour 548
-  Northport 561
-  Amherst 530
-  Reilly 540
-  Arches 549
-  Pemberton 562
-  Andalusia 531
-  Spiva 541
-  Eastbrook 550
-  Freeland 563
-  Santa Monica 532
-  Calais 542
-  New Haven 551
-  Serenity 564

BATH AND SPA

	Reflections 565		Berwick 578
	Bryant 566		Mix & Match 580
	Jayden 567		Lincoln Square 582
	Acadia 568		Regency 583
	Dawson 570		Lawrenceville 584
	Bristol Way 572		Chelsea 585
	Quinton Parlor 574		Cristallo Fiore 586
	Smithfield 575		Heritage 587
	Park Ridge 576		




























































MINI PENDANTS

	Ice Fragments 590		Darien 597		Cassandra 599		Teardrop 602		Predator 604		Firestorm 607		Pierra 610
	Etched Glass 590		Duncan 597		Strata 599		Vesta 602		Gemstones 604		Maui 608		Favela 610
	Hammered Glass 590		Viva 597		Carved Glass 599		Desert Winds 602		Fusion 605		Collage 608		Favelita 610
	Synthesis 591		Watersphere 598		Chromia 600		Andover 603		Capri 605		Venture 608		Iridescence 611
	Menlow Park 592		Ribbed Glass 598		Refraction 600		Coletta 603		Crackle 605		Geval 608		Formations 611
	Orbital 594		Rury 598		Colorwave 601		Piedra 603		Shells 606		Karma 609		Molten 611
	Skylar 594		Jerard 598		Surreal 601		Maple 603		Seashore 606		Garden Breeze 609		Vortex 611
	Cipher 594		Mickley 598		Surrealist 601		Sandstorm 603		Glass Mosaic 606		Sandstone 609		Mini Vortex 611
	Hand Formed Glass 595		Layers 598		Dunes 601		Cira 603		Fissure 607		Granite 609		Galaxy 612
	Geometrics 595		Encapsulate 599		Canyon 601		Vines 604		Fission 607		Abstractions 609		Tidewaters 612
	Danica 596		Cubico 599		Horizon 601		Twister 604		Curvalo 607		Geologic 609		Cilindro 613

MINI PENDANTS

-  Mulino 613
-  Arco Belano 614
-  Milan 615
-  Classico 616
-  Verona 617
-  Lungo 617
-  Mela 618
-  Melony 618
-  Kersey 619
-  Cynthia 620
-  Alea 620
-  Watercube 620
-  Spun Aluminum 621
-  Sorenson 621
-  Chapeau 621
-  Vasso Chromo 621
-  Nestor 621
-  Roxa 621

OUTDOOR

-  Morganview 710
-  Blackwell 712
-  San Gabriel 714
-  Kanso 716
-  Newlton 718
-  San Fernando 720
-  Winona 721
-  Madison 722
-  Costa Mesa 724
-  Rustica 726
-  Lowell 698
-  Bianca 700
-  Mediterraneo 702
-  Lapunte 703
-  Trevot 704
-  Croftwell 705
-  Colby 706
-  Freeport 707
-  Sedona 708
-  Madagascar 728
-  Maritime 730
-  Searsport 732
-  Marina 734
-  Meadowview 735
-  Insulator Glass 736
-  Streetside Cafe 737
-  Portside 738
-  Westport 739
-  Village Lantern 740
-  Barnside 742
-  Farmstead 743
-  Wikshire 744
-  Worthington 745
-  Burlington Junction 746
-  Barrington Gate 748
-  Tuscany Coast 750
-  Glendale 752
-  Riverdale 754
-  Lafayette 755
-  Wellington Park 756
-  Covina 758
-  Provincial 759
-  Forged Provincial 760
-  Forged Brookridge 762
-  Forged Lancaster 764
-  Forged Jefferson 766
-  Jefferson 768
-  Landings 769
-  Manor 770
-  Bristol 771
-  Taos 772
-  Orlean 774
-  Logansport 776
-  Anise 778
-  Acadiana 780
-  Central Square 781
-  Maryville 786
-  Grande Isle 790
-  Bayou 794



RESTORATION

Authentic Turn of the Century Styling



31236/1

31239/9

SLATINGTON

The Slatington collection exhibits an industrial inspired design using layers of metal to create a machine-like presence. The cylindrical shapes are complemented by a wire mesh to further contribute to the restoration appeal. Brushed Nickel accents highlight key details against the Silvered Graphite finish.




Shown as semi-flush 9" H



31237/6



31238/6



31235/1

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31235/1	(1) 60W Med.	6"	13"	-	5"	2 lbs.	
31236/1	(1) 60W Med.	6"	11"	50"	-	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31237/6	(6) 60W Med.	22"	4"	50"	-	7 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31238/6	(6) 60W Med.	22"	14"	59"	-	10 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31239/9	(9) 60W Med.	28"	14"	59"	-	14 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

* Bulb #1092 optional



66894/6




(29" Corner to Corner)



66891/1



66892/1



66890/1



66893/4



LABORATORY

This collection was cleverly designed around our filament tube shaped bulbs by incorporating them into the actual shape of the Weathered Zinc framework. With a socket on one end and a faux socket on the other, the bulbs seem to form a continuous electrified circuit.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66890/1	(1) 60W Med.	5"	20"	-	4"	2 lbs.	ADA Compliant, Bulb #1103 optional
66891/1	(1) 60W Med.	14"	15"	-	3"	3 lbs.	ADA Compliant, Bulb #1099 optional
66892/1*	(1) 60W Med.	14"	14"	58"	-	3 lbs.	Bulb #1099 optional
66893/4*	(4) 60W Med.	44"	11"	60"	11"	6 lbs.	Bulb #1103 optional
66894/6*	(6) 60W Med.	20"	28"	76"	-	8 lbs.	Bulb #1099 optional

* (1) 6", (1) 12" & (1) 24" extension rods w/hang straight included



31790/1



31566/5



31567/6



31565/4



31791/1




31792/1



GARRETT

The Garrett collection reveals a stunning display of large scaled, solid prismatic crystals that are precisely cut for maximum refraction of light. The pieces are set on a minimalist Oil Rubbed Bronze finished frame to further accentuate the windows of crystal.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31565/4	(4) 60W Cand.	14"	13"	51"	-	23 lbs.	Bulb #1101 optional
31566/5	(5) 60W Cand.	18"	16"	54"	-	36 lbs.	Bulb #1101 optional
31567/6	(6) 60W Cand.	24"	15"	55"	-	53 lbs.	Bulb #1101 optional
31790/1	(1) 60W Cand.	6"	10"	-	6"	6 lbs.	Bulb #1101 optional
31791/1	(1) 60W Med.	7"	15"	54"	-	12 lbs.	Bulb #1102 optional
31792/1	(1) 60W Med.	9"	16"	55"	-	16 lbs.	Bulb #1102 optional



RUTHERFORD

This series has a smooth curving profile adorned with a decorative link casting adding to the restoration appeal of these designer pendants. The edge of the metal shade is defined by a ring that has period-authentic thumbscrews and a frosted glass diffuser. Finishes include Polished Nickel, Polished Nickel/Gloss white, Brushed Nickel, Oil Rubbed Bronze, Polished Nickel/Weathered Zinc, and Brushed Antique Brass/Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
57031/1	(1) 100W Med.	15"	13"	52"	-	6 lbs.	Polished Nickel finish
57041/1	(1) 100W Med.	15"	13"	52"	-	6 lbs.	Gloss White Shade, Polished Nickel finish
57051/1	(1) 100W Med.	15"	13"	52"	-	6 lbs.	Brushed Nickel finish
57061/1	(1) 100W Med.	15"	13"	52"	-	6 lbs.	Oil Rubbed Bronze finish
57081/1	(1) 100W Med.	15"	13"	52"	-	6 lbs.	Weathered Zinc Shade, Polished Nickel finish

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included on all above



RUTHERFORD

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
57030/1	(1) 60W Med.	9"	13"	51"	-	4 lbs.	Polished Nickel finish
57032/1	(1) 100W Med.	18"	14"	52"	-	8 lbs.	Polished Nickel finish
57040/1	(1) 60W Med.	9"	13"	51"	-	4 lbs.	Gloss White Shade, Polished Nickel finish
57042/1	(1) 100W Med.	18"	14"	52"	-	8 lbs.	Gloss White Shade, Polished Nickel finish
57050/1	(1) 60W Med.	9"	13"	51"	-	4 lbs.	Brushed Nickel finish
57052/1	(1) 100W Med.	18"	14"	52"	-	8 lbs.	Brushed Nickel finish
57060/1	(1) 60W Med.	9"	13"	51"	-	4 lbs.	Oil Rubbed Bronze finish
57062/1	(1) 100W Med.	18"	14"	52"	-	8 lbs.	Oil Rubbed Bronze finish
57080/1	(1) 60W Med.	9"	13"	51"	-	4 lbs.	Weathered Zinc Shade, Polished Nickel finish
57082/1	(1) 100W Med.	18"	14"	52"	-	8 lbs.	Weathered Zinc Shade, Polished Nickel finish

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included on all above



66850/1



66870/1



66860/1



66880/1



66852/1



66872/1



66862/1



66882/1



CAROLTON

With a vintage industrial look, the Carolton collection is crafted of a large spun shade, accented with die-cast aluminum hardware and an open bottom for direct lighting. Choose between stem mounted or pulldown pendant options. Finishes include Brushed Nickel, Oil Rubbed Bronze, Gloss White/Polished Chrome, and Weathered Zinc/Polished Nickel.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66850/1	(1) 100W Med.	8"	12"	52"	-	4 lbs.	Brushed Nickel finish
66852/1	(1) 100W Med.	13"	14"	54"	-	4 lbs.	Brushed Nickel finish
66860/1	(1) 100W Med.	8"	12"	52"	-	4 lbs.	Oil Rubbed Bronze finish
66862/1	(1) 100W Med.	13"	14"	54"	-	4 lbs.	Oil Rubbed Bronze finish
66870/1	(1) 100W Med.	8"	12"	52"	-	4 lbs.	Gloss White Shade, Polished Chrome finish
66872/1	(1) 100W Med.	13"	14"	54"	-	4 lbs.	Gloss White Shade, Polished Chrome finish
66880/1	(1) 100W Med.	8"	12"	52"	-	4 lbs.	Weathered Zinc shade, Polished Nickel finish
66882/1	(1) 100W Med.	13"	14"	54"	-	4 lbs.	Weathered Zinc shade, Polished Nickel finish

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included on all above



Pulldown

Pulldown

66871/1
[Barcode]

66881/1
[Barcode]

66851/1
[Barcode]



66861/1
[Barcode]



66853/1
[Barcode]

66873/1
[Barcode]

66863/1
[Barcode]

66883/1
[Barcode]

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66851/1	(1) 100W Med.	8"	12"	39-71"	-	5 lbs.	Brushed Nickel finish
66853/1	(1) 100W Med.	12"	14"	39-71"	-	7 lbs.	Brushed Nickel finish
66861/1	(1) 100W Med.	8"	12"	39-71"	-	5 lbs.	Oil Rubbed Bronze finish
66863/1	(1) 100W Med.	12"	14"	39-71"	-	7 lbs.	Oil Rubbed Bronze finish
66871/1	(1) 100W Med.	8"	12"	39-71"	-	5 lbs.	Gloss White Shade, Polished Chrome finish
66873/1	(1) 100W Med.	12"	14"	39-71"	-	7 lbs.	Gloss White Shade, Polished Chrome finish
66881/1	(1) 100W Med.	8"	12"	39-71"	-	5 lbs.	Weathered Zinc shade, Polished Nickel finish
66883/1	(1) 100W Med.	12"	14"	39-71"	-	7 lbs.	Weathered Zinc shade, Polished Nickel finish

CAROLTON



CHADWICK

The Chadwick collection reflects the beauty of hand-turned craftsmanship inspired by early 20th century lighting and antiques that have surpassed the test of time. This robust collection features detailing appropriate for classic or transitional décors. Finishes include Polished Nickel, Satin Nickel, Antique Copper, Oiled Bronze and Gloss White. Frosted glass diffusers and various dome options, including glass, seedy glass and metal allow for adaptability to almost any design scheme.



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66114-1	(1) 100W Med.	13"	14"	-	5 lbs.	Polished Nickel finish
66118-1	(1) 100W Med.	17"	14"	-	9 lbs.	Polished Nickel finish
66124-1	(1) 100W Med.	13"	14"	-	5 lbs.	Satin Nickel finish
66128-1	(1) 100W Med.	17"	14"	-	9 lbs.	Satin Nickel finish
66134-1	(1) 100W Med.	13"	14"	-	5 lbs.	Oiled Bronze finish
66138-1	(1) 100W Med.	17"	14"	-	9 lbs.	Oiled Bronze finish
66144-1	(1) 100W Med.	13"	14"	-	5 lbs.	Antique Copper finish
66148-1	(1) 100W Med.	17"	14"	-	9 lbs.	Antique Copper finish

* 1-6" and 2-12" extension rods with hang straight included on all above



CHADWICK



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66513-1	(1) 100W Med.	13"	14"	46"	-	6 lbs.	Polished Nickel finish, 3' of chain optional
66523-1	(1) 100W Med.	13"	14"	46"	-	6 lbs.	Satin Nickel finish, 3' of chain optional
66533-1	(1) 100W Med.	13"	14"	46"	-	6 lbs.	Oiled Bronze finish, 3' of chain optional
66543-1	(1) 100W Med.	13"	14"	46"	-	6 lbs.	Antique Copper finish, 3' of chain optional
67713-1	(1) 100W Med.	13"	14"	46"	-	5 lbs.	Bulb #1102 optional, Polished Nickel finish
67723-1	(1) 100W Med.	13"	14"	46"	-	5 lbs.	Bulb #1102 optional, Satin Nickel finish
67733-1	(1) 100W Med.	13"	14"	46"	-	5 lbs.	Bulb #1102 optional, Oiled Bronze finish
67743-1	(1) 100W Med.	13"	14"	46"	-	5 lbs.	Bulb #1102 optional, Antique Copper finish

* 1-6" and 2-12" extension rods with hang straight included on all above



CHADWICK



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66113-1	(1) 100W Med.	13"	14"	-	8 lbs.	Polished Nickel finish with White Glass
66123-1	(1) 100W Med.	13"	14"	-	8 lbs.	Satin Nickel finish with White Glass
66133-1	(1) 100W Med.	13"	14"	-	8 lbs.	Oiled Bronze finish with Amber Glass
66143-1	(1) 100W Med.	13"	14"	-	8 lbs.	Antique Copper finish with White Glass
66413-1	(1) 100W Med.	13"	14"	-	8 lbs.	Polished Nickel finish with Cappa Shells
66423-1	(1) 100W Med.	13"	14"	-	8 lbs.	Satin Nickel finish with Cappa Shells
66433-1	(1) 100W Med.	13"	14"	-	8 lbs.	Oiled Bronze finish with Cappa Shells
66443-1	(1) 100W Med.	13"	14"	-	8 lbs.	Antique Copper finish with Cappa Shells
66633-1	(1) 100W Med.	13"	14"	-	8 lbs.	Oiled Bronze finish with White Glass

* 1-6" and 2-12" extension rods with hang straight included on all above



66515-1



66514-1



66516-1



66525-1



66524-1



66526-1



67732-1



67742-1



67722-1



67712-1



CHADWICK

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66514-1	(1) 100W Med.	8"	14"	46"	-	5 lbs.	Polished Nickel finish, Gloss White shade
66524-1	(1) 100W Med.	8"	14"	46"	-	5 lbs.	Satin Nickel finish, Gloss White shade
66515-1	(1) 100W Med.	13"	14"	46"	-	5 lbs.	Polished Nickel finish, Gloss White shade
66525-1	(1) 100W Med.	13"	14"	46"	-	5 lbs.	Satin Nickel finish, Gloss White shade
66516-1	(1) 100W Med.	17"	14"	47"	-	9 lbs.	Polished Nickel finish, Gloss White shade
66526-1	(1) 100W Med.	17"	14"	47"	-	9 lbs.	Satin Nickel finish, Gloss White shade
67712-1	(1) 100W Med.	8"	14"	46"	-	5 lbs.	Bulb #1092 optional, Antique Copper finish
67722-1	(1) 100W Med.	8"	14"	46"	-	5 lbs.	Bulb #1092 optional, Oiled Bronze finish
67732-1	(1) 100W Med.	8"	14"	46"	-	5 lbs.	Bulb #1092 optional, Polished Nickel finish
67742-1	(1) 100W Med.	8"	14"	46"	-	5 lbs.	Bulb #1092 optional, Satin Nickel finish

* 1-6" and 2-12" extension rods with hang straight included on all above

66120-3



66771-1



66761-1



66751-1



66781-1



66119-1



66139-1



66149-1



66159-1



11453/3



11463/3



66760-1



66780-1



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66119-1*	(1) 100W Med.	8"	14"	-	5 lbs.	Satin Nickel finish
66120-3*	(3) 100W Med.	22"	18"	-	13 lbs.	Satin Nickel finish
66139-1*	(1) 100W Med.	8"	14"	-	5 lbs.	Oiled Bronze finish
66149-1*	(1) 100W Med.	8"	14"	-	5 lbs.	Antique Copper finish
66159-1*	(1) 100W Med.	8"	14"	-	5 lbs.	Polished Nickel finish

* 1-6" and 2-12" extension rods with hang straight included

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11443/3	(3) 60W Cand.	15"	5"	-	8 lbs.	Polished Nickel finish, clear ribbed glass
11453/3	(3) 60W Cand.	15"	5"	-	8 lbs.	Oiled Bronze finish, clear ribbed glass
11463/3	(3) 60W Cand.	15"	5"	-	8 lbs.	Brushed Nickel finish, clear ribbed glass
66751-1*	(1) 100W Med.	7"	16"	-	6 lbs.	Antique Copper finish, Bulb #1092 optional
66760-1	(1) 100W Med.	7"	15"	8"	6 lbs.	Oiled Bronze finish, Bulb #1092 optional
66761-1*	(1) 100W Med.	7"	16"	-	6 lbs.	Oiled Bronze finish, Bulb #1092 optional
66771-1*	(1) 100W Med.	7"	16"	-	6 lbs.	Satin Nickel finish, Bulb #1092 optional
66780-1	(1) 100W Med.	7"	15"	8"	6 lbs.	Polished Nickel finish, Bulb #1092 optional
66781-1*	(1) 100W Med.	7"	16"	-	6 lbs.	Polished Nickel finish, Bulb #1092 optional

* 1-6" and 2-12" extension rods with hang straight included

Brushed Nickel finish is the same as our Satin Nickel finish.

CHADWICK



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66112-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Polished Nickel finish with White Glass
66122-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Satin Nickel finish with White Glass
66132-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Oiled Bronze finish with Amber Glass
66142-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Antique Copper finish with White Glass
66632-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Oiled Bronze finish with White Glass

* 1-6" and 2-12" extension rods with hang straight included

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66110-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Polished Nickel finish with White Glass
66111-2	(2) 60W Med.	13"	5"	-	6 lbs.	Polished Nickel finish with White Glass
66121-2	(2) 60W Med.	13"	5"	-	6 lbs.	Satin Nickel finish with White Glass
66130-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Oiled Bronze finish with Amber Glass
66131-2	(2) 60W Med.	13"	5"	-	6 lbs.	Oiled Bronze finish with Amber Glass
66141-2	(2) 60W Med.	13"	5"	-	6 lbs.	Antique Copper finish with White Glass
66630-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Oiled Bronze finish with White Glass
66631-2	(2) 60W Med.	13"	5"	-	6 lbs.	Oiled Bronze finish with White Glass

CHADWICK



66412-1



66422-1



66432-1



66442-1



66411-2



66421-2



66431-2



66441-2



66410-1



66430-1



CHADWICK

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66410-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Polished Nickel finish with Cappa Shells
66411-2	(2) 60W Med.	13"	5"	-	6 lbs.	Polished Nickel finish with Cappa Shells
66412-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Polished Nickel finish with Cappa Shells
66421-2	(2) 60W Med.	13"	5"	-	6 lbs.	Satin Nickel finish with Cappa Shells
66422-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Satin Nickel finish with Cappa Shells
66430-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Oiled Bronze finish with Cappa Shells
66431-2	(2) 60W Med.	13"	5"	-	6 lbs.	Oiled Bronze finish with Cappa Shells
66432-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Oiled Bronze finish with Cappa Shells
66441-2	(2) 60W Med.	13"	5"	-	6 lbs.	Antique Copper finish with Cappa Shells
66442-1*	(1) 100W Med.	6"	17"	-	6 lbs.	Antique Copper finish with Cappa Shells

* 1-6" and 2-12" extension rods with hang straight included



66115-3



66135-3



66125-3



66145-3



66155-3



66165-3

CHADWICK

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66115-3	(3) 100W Med.	47"	21"	53"	13"	15 lbs.	Polished Nickel finish
66125-3	(3) 100W Med.	47"	21"	53"	13"	15 lbs.	Satin Nickel finish
66135-3	(3) 100W Med.	47"	21"	53"	13"	15 lbs.	Oiled Bronze finish
66145-3	(3) 100W Med.	47"	21"	53"	13"	15 lbs.	Antique Copper finish
66155-3	(3) 100W Med.	47"	21"	53"	13"	15 lbs.	Polished Nickel finish, Gloss White shades
66165-3	(3) 100W Med.	47"	21"	53"	13"	15 lbs.	Satin Nickel finish, Gloss White shades

* 1-6" and 2-12" extension rods with hang straight included



66215-3



66415-3



66635-3



66425-3



66225-3



66435-3



66235-3



66445-3



66245-3

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66215-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Polished Nickel finish with White Glass
66225-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Satin Nickel finish with White Glass
66235-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Oiled Bronze finish with Amber Glass
66245-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Antique Copper finish with White Glass
66415-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Polished Nickel finish with Cappa Shells
66425-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Satin Nickel finish with Cappa Shells
66435-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Oiled Bronze finish with Cappa Shells
66445-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Antique Copper finish with Cappa Shells
66635-3	(3) 100W Med.	47"	21"	13"	24 lbs.	Oiled Bronze finish with White Glass

* 1-6" and 2-12" extension rods with hang straight included

CHADWICK



66163-5



66153-5



66173-5



66183-5



66673-5



66160-1



66670-1



66150-1



66170-1



66180-3



BROOKSDALE

Blending vintage design elements with today's casual living, the Brooksdale collection's functional beauty allows for use in a variety of decors. Choose the finish that best reflects your style; Polished Chrome, Satin Nickel, or Antique Copper with white glass or Oiled Bronze with amber glass or white glass.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66150-1	(1) 100W Med.	5"	13"	7"	3 lbs.	Polished Chrome finish with White Glass
66153-5*	(5) 100W Med.	25"	14"	-	14 lbs.	Polished Chrome finish with White Glass
66160-1	(1) 100W Med.	5"	13"	7"	3 lbs.	Satin Nickel finish with White Glass
66163-5*	(5) 100W Med.	25"	14"	-	14 lbs.	Satin Nickel finish with White Glass
66170-1	(1) 100W Med.	5"	13"	7"	3 lbs.	Oiled Bronze finish with Amber Glass
66173-5*	(5) 100W Med.	25"	14"	-	14 lbs.	Oiled Bronze finish with Amber Glass
66180-1	(1) 100W Med.	5"	13"	7"	3 lbs.	Antique Copper finish with White Glass
66183-5*	(5) 100W Med.	25"	14"	-	14 lbs.	Antique Copper finish with White Glass
66670-1	(1) 100W Med.	5"	13"	7"	3 lbs.	Oiled Bronze finish with White Glass
66673-5*	(5) 100W Med.	25"	14"	-	14 lbs.	Oiled Bronze finish with White Glass

* 1-6" and 2-12" extension rods with hang straight included



BROOKSDALE

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66151-1	(1) 100W Med.	5"	11"	-	4 lbs.	Polished Chrome finish with White Glass
66152-3	(3) 100W Med.	20"	10"	-	9 lbs.	Polished Chrome finish with White Glass
66161-1	(1) 100W Med.	5"	11"	-	4 lbs.	Satin Nickel finish with White Glass
66162-3	(3) 100W Med.	20"	10"	-	9 lbs.	Satin Nickel finish with White Glass
66171-1	(1) 100W Med.	5"	11"	-	4 lbs.	Oiled Bronze finish with Amber Glass
66172-3	(3) 100W Med.	20"	10"	-	9 lbs.	Oiled Bronze finish with Amber Glass
66181-1	(1) 100W Med.	5"	11"	-	4 lbs.	Antique Copper finish with White Glass
66182-3	(3) 100W Med.	20"	10"	-	9 lbs.	Antique Copper finish with White Glass
66671-1	(1) 100W Med.	5"	11"	-	4 lbs.	Oiled Bronze finish with White Glass
66672-3	(3) 100W Med.	20"	10"	-	9 lbs.	Oiled Bronze finish with White Glass

* 1-6" and 2-12" extension rods with hang straight included on all above



55010/1



55040/1



55030/1



55020/1

NEWBERRY

This series has a vintage character in both style and detailing with a spun metal shade held by a solid cast socket holder. The backplate has crisp lines etched into its material that reflect the shade elements. Finishes include Polished Nickel, Brushed Nickel, Antique Copper, and Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
55010/1	(1) 100W Med.	11"	9"	-	9"	2 lbs.	Polished Nickel finish, Bulb #1092 optional
55011/1	(1) 100W Med.	11"	7"	81"	-	2 lbs.	Polished Nickel finish, Bulb #1092 optional
55020/1	(1) 100W Med.	11"	9"	-	9"	2 lbs.	Brushed Nickel finish, Bulb #1092 optional
55021/1	(1) 100W Med.	11"	7"	81"	-	2 lbs.	Brushed Nickel finish, Bulb #1092 optional
55030/1	(1) 100W Med.	11"	9"	-	9"	2 lbs.	Antique Copper finish, Bulb #1092 optional
55031/1	(1) 100W Med.	11"	7"	81"	-	2 lbs.	Antique Copper finish, Bulb #1092 optional
55040/1	(1) 100W Med.	11"	9"	-	9"	2 lbs.	Oil Rubbed Bronze finish, Bulb #1092 optional
55041/1	(1) 100W Med.	11"	7"	81"	-	2 lbs.	Oil Rubbed Bronze finish, Bulb #1092 optional



14214/5+1




14213/4+1




14212/3+1




14210/1




14211/3


PALACIAL

The Palacial collection features a cascade of prismatic crystals suspended from an Oil Rubbed Bronze frame. Each of the crystal's thick triangular profile bend light into various angles enhancing its visual depth and beauty.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14210/1	(1) 60W Cand.	10"	22"	-	-	12 lbs.	
14211/3	(3) 60W Cand.	16"	62"	-	-	30 lbs.	
14212/3+1	(4) 60W Cand.	16"	20"	58"	-	13 lbs.	
14213/4+1	(5) 60W Cand.	20"	21"	59"	-	16 lbs.	
14214/5+1	(6) 60W Cand.	24"	22"	60"	-	25 lbs.	



Close-up of canopy



11827/5



11826/4



11825/3



PESARO

A textural mesh pattern is created through the use of jewelry chains through which light is softly diffused. Finished in Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11825/3	(3) 60W Med.	16"	9"	-	-	5 lbs.	
11826/4	(4) 60W Med.	24"	13"	-	-	11 lbs.	
11827/5	(5) 60W Cand.	21"	31"	69"	-	11 lbs.	




31512/8



31510/1



31511/6



PERRY

The character of this linear fixture is evident through the use of a wire mesh enclosure that diffuses and softens the light presentation. The metalwork is hand finished with our exclusive Malted Rust finish.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31510/1	(1) 60W Med.	6"	13"	52"	-	4 lbs.	Bulb #1092 optional
31511/6	(6) 60W Cand.	40"	22"	61"	15"	16 lbs.	Bulb #1103 optional
31512/8	(8) 60W Cand.	53"	22"	61"	15"	20 lbs.	Bulb #1103 optional



Close-up of canopy



31820/6



31821/12



LEWISBURG

This series exudes a refined, Mediterranean design made with a solid iron ring that anchors the lights around its perimeter. Our exclusive Malted Rust finish embellishes the metalwork, delivering subtle sophistication. For a more restoration style, pair with filament bulbs for a warm ambiance.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31820/6	(6) 60W Cand.	21"	19"	58"	-	7 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31821/12	(12) 60W Cand.	27"	21"	60"	-	10 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included

* Bulb #1101 optional



65150-2

Pulldown



65151-3

Pulldown

FARMHOUSE

Inspired by antique lighting, this series recalls turn-of-the-century design where simple aesthetics and mechanical function combined to create charming, yet versatile fixtures. These classic pull-downs have a decorative weight that counterbalances the fixture for easy height adjustability anytime by simply pulling down or lifting up on the fixture.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
65150-2	(2) 100W Med.	44"	30-49"	13"	17 lbs.	Oiled Bronze
65151-3	(3) 100W Med.	56"	33-54"	13"	24 lbs.	Oiled Bronze



65081-1




65071-1


Pulldown



65061-1




65070-1




65080-1




65060-1


Pulldown



65090-1


FARMHOUSE

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
65060-1	(1) 100W Med.	8"	39-71"	-	6 lbs.	Bellwether Copper
65061-1	(1) 100W Med.	14"	39-70"	-	7 lbs.	Bellwether Copper
65070-1	(1) 100W Med.	8"	39-71"	-	6 lbs.	Oiled Bronze
65071-1	(1) 100W Med.	14"	39-70"	-	7 lbs.	Oiled Bronze
65080-1	(1) 100W Med.	8"	39-71"	-	6 lbs.	Aged Pewter
65081-1	(1) 100W Med.	14"	39-70"	-	7 lbs.	Aged Pewter
65090-1	(1) 100W Med.	7"	39-70"	-	5 lbs.	Oiled Bronze with White Glass



65049-1

010-AC

65072-1

65073-1

65051-1

D2252

D2254

Pull-down

Pull-down

F A R M H O U S E

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
010-AC	(1) 60W Med. Torpedo	7"	9"	-	2 lbs.	Antique Copper, Includes 6 feet of Cord
65049-1	(1) 60W Med.	12"	13"	-	5 lbs.	Bellwether Copper
65051-1	(1) 60W Med.	15"	42-63"	-	8 lbs.	Antique Brass
65072-1	(1) 13W Med. (CFL only)	12"	32"	17"	20 lbs.	Oiled Bronze
65073-1	(1) 13W Med. (CFL only)	16"	69"	26"	46 lbs.	Oiled Bronze
D2252	(1) 100W Med.	12"	32"	17"	18 lbs.	Antique Brass, Bulb #1092 optional
D2254	(1) 100W Med.	15"	69"	26"	46 lbs.	Antique Brass, Bulb #1092 optional



55047/3



55045/1



Pulldown



55046/2



WILMINGTON

The Wilmington collection has a classic design style to enhance a variety of settings. A pull-down single pendant offers added versatility and function to the series that is finished in Oil Rubbed Bronze with opal white glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
55045/1	(1) 100W Med.	14"	39-72"	-	-	13 lbs.	
55046/2	(2) 100W Med.	47"	16"	51"	14"	14 lbs.	
55047/3	(3) 100W Med.	59"	16"	51"	14"	18 lbs.	



46232/24



46230/12



46231/12

DELPHINE

The collection displays an explosion of light from a center core with optional vintage bulbs and thin arms on a starburst style frame finished in Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46230/12	(12) 60W Med.	16"	16"	43"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
46231/12	(12) 60W Med.	27"	27"	47"	-	6 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
46232/24	(24) 60W Med.	36"	36"	50"	-	11 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included

* Bulb # 1102 optional



66910/4



66911/6



66912/10



XENIA

These fixtures showcase a unique linear design with unequal length arms that pass through the fixture's central connection. The metal arms can be easily adjusted from a near parallel position to a loosely gathered look. An Oil Rubbed Bronze finish and optional filament bulbs complete this innovative series.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66910/4	(4) 60W Med.	5"	20"	-	9"	3 lbs.	
66911/6	(6) 60W Med.	31"	16"	55"	18"	6 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
66912/10	(10) 60W Med.	40"	25"	60"	22"	8 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

* Bulb #1102 optional



HARTFORD

The minimalist profiles of the Hartford Collection allow them unlimited versatility. The generously spaced arms present a light, airy tone, which is further accentuated by the Oil-Rubbed finish.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
281-OB	(1) 60W Cand.	5"	10"	-	2 lbs.	
283-OB	(3) 60W Cand.	18"	17"	-	6 lbs.	
286-OB	(6) 60W Cand.	25"	24"	-	11 lbs.	
289-OB	(9) 60W Cand.	29"	28"	-	17 lbs.	



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
63024-1	(1) 100W Med.	7"	12"	-	3 lbs.	Bulb #1092 optional
63025-1	(1) 100W Med.	6"	12"	-	3 lbs.	Bulb #1092 optional
63034-1	(1) 100W Med.	7"	12"	-	3 lbs.	Bulb #1092 optional
63035-1	(1) 100W Med.	6"	12"	-	3 lbs.	Bulb #1092 optional

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14260/1	(1) 60W Med.	13"	18"	-	14"	7 lbs.	Bulb #1092 optional
14261/1	(1) 60W Med.	13"	18"	50"	-	7 lbs.	Bulb #1092 optional (1) 6" & (2) 12" extension rods w/hang straight included
14262/3	(3) 40W Cand.	15"	19"	51"	-	10 lbs.	Bulb #1101 optional (1) 6" & (2) 12" extension rods w/hang straight included

BROOKLINE

This unique pendant collection takes advantage of a shapely clear glass shade which serves as a "window" to the finely detailed metalwork behind the glass. A removable ring on the bottom edge of the glass allows you to change up your decor on a moment's notice. Finishes include Polished Nickel and Oiled Bronze.

ENCOMPASS

A clear hand-blown glass sphere is cleverly held by a unique framework that envelops and clasps the glass to transform and inspire a room setting. Finished in Oil Rubbed Bronze with brass accents.



Close-up of canopy



PARK RIDGE

This series features turn-of-the-century styling with spun accents finished in an Oil Rubbed Bronze. The reeded light amber glass provides a warm glow when illuminated, establishing an idyllic ambiance within a room setting.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11650/1	(1) 60W Med.	5"	9"	-	8"	2 lbs.	
11651/2	(2) 60W Med.	11"	9"	-	8"	4 lbs.	
11652/3	(3) 60W Med.	19"	9"	-	8"	5 lbs.	
11653/4	(4) 60W Med.	26"	9"	-	8"	7 lbs.	
11654/2	(2) 60W Med.	13"	11"	-	-	4 lbs.	
11655/3	(3) 60W Med.	15"	20"	59"	-	7 lbs.	
11656/5	(5) 60W Med.	25"	26"	65"	-	11 lbs.	



63056-5

63055-6



63058-8

NATURAL ROPE

This collection transforms natural rope from a functional material to a unique decorative element adding color, texture, and material that contrasts nicely with the Aged Bronze or Silvered Graphite finished metalwork with Brushed Nickel accents. The Aged Bronze finish comes with either tan linen shades or opal white glass. The Silvered Graphite finish may be complimented by our optional decorative filament bulbs.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
63055-6	(6) 60W Med.	31"	31"	70"	13"	15 lbs.	
63056-5	(5) 60W Med.	20"	25"	64"	-	9 lbs.	
63058-8	(8) 60W Med.	35"	44"	83"	-	20 lbs.	


* Bulb #1102 optional



63054-3



63052-2



63053-1



63050-1



63051-2



63057-6

NATURAL ROPE

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
63050-1	(1) 100W Med.	11"	15"	-	12-26"	4 lbs.	Shade included, Comes w/cord cover and plug that can be removed for direct wiring into junction box.
63051-2	(2) 60W Med.	10"	17"	-	6"	4 lbs.	
63052-2	(2) 60W Med.	15"	14"	-	-	8 lbs.	
63053-1	(1) 60W Med.	4"	26"	68"	-	3 lbs.	
63054-3	(3) 60W Med.	20"	26"	65"	-	13 lbs.	
63057-6	(6) 60W Med.	25"	31"	71"	-	13 lbs.	

* Bulb #1102 optional



63015-5



63019-6



63017-8



73046-3

NATURAL ROPE

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
63015-5	(5) 60W Cand.	25"	25"	-	9 lbs.	Shades included
63017-8	(8) 60W Cand.	42"	44"	-	20 lbs.	Shades included
63019-6	(6) 60W Cand.	36"	31"	-	15 lbs.	Shades included
73046-3	(3) 100W Med.	54"	19"	-	9 lbs.	Shades included



63010-2



63011-2



63016-6



63012-1



63013-3



63060-1



63014-4



NATURAL ROPE



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
63010-2	(2) 60W Cand.	12"	17"	7"	4 lbs.	Shades included
63011-2	(2) 60W Med.	15"	14"	-	8 lbs.	
63012-1	(1) 60W Med.	4"	26"	-	3 lbs.	Includes 3 ft. of chain
63013-3	(3) 60W Med.	20"	26"	-	13 lbs.	
63014-4	(4) 60W Med.	26"	30"	-	20 lbs.	
63016-6	(6) 60W Cand.	30"	32"	-	13 lbs.	Shades included
63060-1	(1) 100W Med.	11"	15"	12-26"	4 lbs.	Shade included, Comes w/cord cover and plug that can be removed for direct wiring into junction box.



NATURAL ROPE

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
63018-6	(6) 60W Cand.	35"	31"	-	17 lbs.	
63040-2	(2) 60W Cand.	11"	19"	6"	6 lbs.	
63041-5	(5) 60W Cand.	25"	25"	-	10 lbs.	
63042-6	(6) 60W Cand.	29"	32"	-	13 lbs.	
63043-8	(8) 60W Cand.	41"	44"	-	20 lbs.	
73045-3	(3) 75W Med.	54"	17"	-	9 lbs.	



15900/1



15903/8



15901/4



15904/14



15902/5



PEARCE

This collection showcases natural rope wrapped around a durable metal frame. The Matte Black finished frame is a perfect contrast to the textures of the organic fibers. Our optional antique filament bulbs can convey a more nostalgic or romantic ambiance.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
15900/1	(1) 60W Med.	8"	20"	-	9"	3 lbs.	Bulb #1099 optional
15901/4	(4) 60W Med.	17"	35"	73"	-	10 lbs.	Bulb #1099 optional
15902/5	(5) 60W Med.	32"	35"	73"	-	15 lbs.	Bulb #1099 optional
15903/8	(8) 60W Med.	31"	24"	63"	-	13 lbs.	Bulb #1102 optional
15904/14	(14) 60W Med.	43"	24"	61"	24"	19 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included Bulb #1102 optional



31509/6



31506/4



31507/4



31508/4



31505/1

A L A N N A

This series captures the simplicity and charm of the delicate lines of a wrought iron greenhouse. The Oil Rubbed Bronze finished frame is designed with subtle angles that soften the edges while large panels of clear glass define its structure.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31505/1	(1) 60W Med.	10"	15"	-	5"	5 lbs.	Bulb #1092 Optional
31506/4	(4) 60W Cand.	12"	11"	-	-	8 lbs.	
31507/4	(4) 60W Cand.	14"	17"	-	-	27 lbs.	
31508/4	(4) 60W Cand.	32"	15"	55"	10"	19 lbs.	
31509/6	(6) 60W Cand.	54"	23"	97"	17"	46 lbs.	



10193/6



10192/4



10393/6



10392/4

HEMISPHERES

This dynamic series utilizes the simple geometric shape of circles to form an architectural styled sphere. The crafted metalwork with elegant suspension rods are finished in either Polished Nickel or Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
10192/4	(4) 60W Cand.	24"	37"	75"	-	14 lbs.	Polished Nickel finish
10193/6	(6) 60W Cand.	32"	51"	89"	-	18 lbs.	Polished Nickel finish
10392/4	(4) 60W Cand.	24"	37"	75"	-	14 lbs.	Oil Rubbed Bronze finish
10393/6	(6) 60W Cand.	32"	51"	89"	-	18 lbs.	Oil Rubbed Bronze finish



66280-2



66282-6



22020/1



22021/3

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66280-2	(2) 60W Cand.	11"	13"	6"	6 lbs.	
66282-6	(6) 60W Cand.	14"	22"	-	15 lbs.	

C H E S A P E A K E


Lanterns have historically graced our foyer entrances as a welcoming light that invites the guest into the home. Today, lanterns are not restricted to one location and are often placed throughout the home. This series has a refined design using thick metalwork, decorative turnings, and clear curved glass panels. Finished in Oiled Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
22020/1	(1) 60W Med.	12"	13"	52"	-	7 lbs.	
22021/3	(3) 60W Cand.	16"	18"	57"	-	12 lbs.	

R A N D O L P H

This classic globe pendant features curved bound glass with solid Brushed Brass construction.



31484/3+3




31482/1




31481/2




31480/1




31483/5



RIALTO

The Rialto series showcases a design that allows for appreciation of the solid metal inner structure visible through a delicate transparent metal mesh. The Aged Brass finish assists in discreetly defining the curvaceous shape of this timeless collection.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31480/1	(1) 60W Med.	8"	10"	-	4"	4 lbs.	Bulb #1092 optional, Pocket Sconce, ADA compliant
31481/2	(2) 60W Med.	13"	5"	-	-	4 lbs.	Bulb #1092 optional
31482/1	(1) 60W Med.	6"	8"	88"	-	3 lbs.	Bulb #1092 optional
31483/5	(5) 60W Cand.	22"	11"	56"	-	11 lbs.	Bulb #1101 optional
31484/3+3	(6) 60W Cand.	16"	30"	69"	-	15 lbs.	Bulb #1101 optional



10130/5+5+5



10128/3



Shown as semiflush




10129/5




Shown as semiflush



10126/2



10360/1



10127/3

BRAXTON

Offering a new elevated level of quality and design in a drum pendant, the Braxton collection uses ribbed glass cylinders with crystal-like optics that create a continuous beam of crisp light. Finished in Polished Nickel or Aged Bronze, this series offers elegant sophistication for classic to contemporary décor.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10126/2	(2) 100W Med.	14"	4"	4"	3 lbs.	ADA Compliant
10127/3	(3) 100W Med.	28"	4"	4"	5 lbs.	ADA Compliant
10128/3	(3) 60W Med.	16"	8"	-	11 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
10129/5	(5) 60W Med.	24"	8"	-	17 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
10130/5+5+5	(15) 60W Cand.	24"	21"	-	38 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
10360/1	(1) 60W Med.	6"	8"	4"	2 lbs.	ADA Compliant



10231/6



10167/6



10241/6



10328/3



Shown as semiflush



10329/5



10326/2



10327/3



BRAXTON

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10167/6	(6) 60W Cand.	26"	27"	-	14 lbs.	
10231/6	(6) 60W Cand.	29"	24"	-	10 lbs.	
10241/6	(6) 60W Cand.	29"	24"	-	10 lbs.	
10326/2	(2) 100W Med.	14"	4"	4"	3 lbs.	ADA Compliant
10327/3	(3) 100W Med.	28"	4"	4"	5 lbs.	ADA Compliant
10328/3	(3) 60W Med.	16"	8"	-	11 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
10329/5	(5) 60W Med.	24"	8"	-	17 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31420/1	(1) 60W Med.	8"	10"	-	4"	3 lbs.	ADA compliant
31421/2	(2) 60W Med.	12"	5"	-	-	4 lbs.	
31422/3	(3) 60W Med.	16"	5"	-	-	6 lbs.	
31423/1	(1) 60W Med.	6"	8"	54"	-	4 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
31424/3	(3) 60W Med.	16"	9"	53"	-	9 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included Semi flush mount adaptable

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66418/2	(2) 60W Med.	13"	5"	-	-	7 lbs.	
66419/3	(3) 60W Med.	17"	5"	-	-	10 lbs.	

DIAMOND PLATE


This collection captures the industrial beauty of diamond tread aluminum in an innovative manner. Thick sheets of aluminum are formed into a drum shape and complemented by a Brushed Nickel frame and a frosted glass diffuser.

BRENDON

The Brendon flush mount has a sleek ribbed drum shape finished in Oil Rubbed Bronze and a frosted glass diffuser.




46122/2





46123/3


46125/3

46120/2

46121/3


46124/3


LINDEN MANOR

The Linden Manor collection features a drum shape made from a textural wall of metal or crystal. A frosted glass diffuser (metal items) or textured clear glass (crystal items) is cleverly recessed into the drum for a smooth, seamless appearance. Various finishes, including Polished Nickel, Brushed Nickel, Aged Brass and Oil Rubbed Bronze are adaptable into any color scheme.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46120/2	(2) 60W Med.	12"	5"	-	-	9 lbs.	Aged Brass finish
46121/3	(3) 60W Med.	16"	5"	-	-	14 lbs.	Aged Brass finish
46122/2	(2) 60W Med.	12"	5"	-	-	10 lbs.	Aged Brass finish
46123/3	(3) 60W Med.	16"	5"	-	-	15 lbs.	Aged Brass finish
46124/3	(3) 100W Med.	20"	26"	80"	-	21 lbs.	Aged Brass finish
46125/3	(3) 100W Med.	20"	26"	80"	-	22 lbs.	Aged Brass finish



46102/2



46103/3



46105/3



46100/2



46101/3



46104/3



LINDEN MANOR

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46100/2	(2) 60W Med.	12"	5"	-	-	9 lbs.	Polished Nickel finish
46101/3	(3) 60W Med.	16"	5"	-	-	14 lbs.	Polished Nickel finish
46102/2	(2) 60W Med.	12"	5"	-	-	10 lbs.	Polished Nickel finish
46103/3	(3) 60W Med.	16"	5"	-	-	15 lbs.	Polished Nickel finish
46104/3	(3) 100W Med.	20"	26"	80"	-	21 lbs.	Polished Nickel finish
46105/3	(3) 100W Med.	20"	26"	80"	-	22 lbs.	Polished Nickel finish




46132/2



46133/3



46135/3



46130/2



46131/3




46134/3



LINDEN MANOR

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46130/2	(2) 60W Med.	12"	5"	-	-	9 lbs.	Oil Rubbed Bronze finish
46131/3	(3) 60W Med.	16"	5"	-	-	14 lbs.	Oil Rubbed Bronze finish
46132/2	(2) 60W Med.	12"	5"	-	-	10 lbs.	Oil Rubbed Bronze finish
46133/3	(3) 60W Med.	16"	5"	-	-	15 lbs.	Oil Rubbed Bronze finish
46134/3	(3) 100W Med.	20"	26"	80"	-	21 lbs.	Oil Rubbed Bronze finish
46135/3	(3) 100W Med.	20"	26"	80"	-	22 lbs.	Oil Rubbed Bronze finish




46112/2




46113/3


46115/3

46110/2




46111/3


46114/3




LINDEN MANOR

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46110/2	(2) 60W Med.	12"	5"	-	-	9 lbs.	Brushed Nickel finish
46111/3	(3) 60W Med.	16"	5"	-	-	14 lbs.	Brushed Nickel finish
46112/2	(2) 60W Med.	12"	5"	-	-	10 lbs.	Brushed Nickel finish
46113/3	(3) 60W Med.	16"	5"	-	-	15 lbs.	Brushed Nickel finish
46114/3	(3) 100W Med.	20"	26"	80"	-	21 lbs.	Brushed Nickel finish
46115/3	(3) 100W Med.	20"	26"	80"	-	22 lbs.	Brushed Nickel finish



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66315/1	(1) 60W Med.	4"	11"	85"	-	2 lbs.	Includes 6 feet of brown cord, Polished Chrome finish
66316/1	(1) 60W Med.	4"	11"	85"	-	2 lbs.	Includes 6 feet of brown cord, Polished Chrome finish
66317/1	(1) 60W Med.	4"	11"	86"	-	2 lbs.	Includes 6 feet of brown cord, Polished Chrome finish
66325/1	(1) 60W Med.	4"	11"	85"	-	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
66326/1	(1) 60W Med.	4"	11"	85"	-	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

* Bulb #1099 optional

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66350/1	(1) 60W Med.	12"	9"	42"	-	8 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
66351/1	(1) 60W Med.	17"	12"	45"	-	15 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
66360/1	(1) 60W Med.	12"	9"	42"	-	8 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
66361/1	(1) 60W Med.	17"	12"	45"	-	15 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included

FULTON

With a nod toward the machine age, these pendants have a tubular shape with an industrial flange top. Finishes include Oil Rubbed Bronze and Polished Chrome.

BRAIDEN

This pendant collection offers oversized industrial scale with steel strapping that clutches the substantial band detail. The turned knob details accentuate the design and function to support the bottom glass diffuser. Finishes include Polished Chrome or Oil Rubbed Bronze with complimenting frosted glass.



11821/3



11811/3



11820/2



11810/2



17248/1



17258/1



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11810/2	(2) 60W Med.	10"	5"	-	-	3 lbs.	
11811/3	(3) 60W Med.	14"	5"	-	-	5 lbs.	
11820/2	(2) 60W Med.	10"	5"	-	-	3 lbs.	
11821/3	(3) 60W Med.	14"	5"	-	-	5 lbs.	

SIMPSON

Understated design attributes coupled with function and versatility give these flushes range to fit within a variety of style themes. Frosted white diffuser beautifully contrasts with the metalwork finished in Brushed Nickel or Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17248/1	(1) 75W Med.	12"	9"	-	-	3 lbs.	
17258/1	(1) 75W Med.	12"	9"	-	-	3 lbs.	

ANZA

This semi flush has a low profile opal white glass and a complimenting mechanical frame in either Brushed Nickel or Oil Rubbed Bronze.



17208/1

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17208/1	(1) 75W Med.	7"	10"	84"	-	2 lbs.	

MURPHY

Industrial style mini pendant in Oil Rubbed Bronze.



55001/1



55002/3



55003/4



55000/1

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
55000/1	(1) 100W Med.	5"	11"	-	6"	2 lbs.	
55001/1	(1) 100W Med.	6"	10"	54"	-	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
55002/3	(3) 100W Med.	16"	12"	56"	-	6 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
55003/4	(4) 100W Med.	36"	12"	56"	10"	12 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

* Bulb #1092 optional

BRISBANE

The Brisbane collection exhibits weaved wire formed into a drum shape and accented with stepped socket hardware. This series is finished in Polished Chrome with vintage Edison bulbs available as an option.



31210/1
31211/2
31212/1



31213/4

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31210/1	(1) 60W Med.	7"	12"	4"	5 lbs.	ADA Compliant, Bulb #1092 optional
31211/2	(2) 60W Med.	12"	5"	-	7 lbs.	Bulb #1092 optional
31212/1	(1) 60W Med.	10"	39-57"	-	11 lbs.	Bulb #1092 optional
31213/4	(4) 60W Med.	47"	32-51"	8"	23 lbs.	Bulb #1092 optional

PARAMETERS - NICKEL

This series showcases a minimalist angular design with a modern-traditionalist edge. Polished Nickel metal framework elegantly displays the clear glass panels while optional filament bulbs offer a decorative focal point to the functional aspects of the series.



63020-1
63021-2
63022-1



63023-4

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
63020-1	(1) 60W Med.	7"	12"	4"	5 lbs.	ADA Compliant, Bulb #1092 optional
63021-2	(2) 60W Med.	12"	5"	-	7 lbs.	Bulb #1092 optional
63022-1	(1) 60W Med.	10"	39-57"	-	11 lbs.	Bulb #1092 optional
63023-4	(4) 60W Med.	47"	32-51"	8"	23 lbs.	Bulb #1092 optional

PARAMETERS - BRONZE

This series showcases a minimalist angular design with clear glass panels displayed by the Oiled Bronze metal framework. Optional filament bulbs offer a decorative focal point to the functional aspects of the series.




Shown angled



17241/1



17251/1



17231/1



17242/1



17252/1



17232/1



17240/2



17250/2



17230/2



URBANO

This series features sleek curves, substantial metalwork and authentic halophane glass diffusers. Finishes include Polished Chrome, Brushed Nickel, and Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17230/2	(2) 60W Med.	13"	5"	-	-	5 lbs.	Polished Chrome finish
17231/1*	(1) 60W Med.	10"	10"	47"	8"	5 lbs.	Polished Chrome finish
17232/1*	(1) 75W Med.	13"	8"	47"	-	6 lbs.	Polished Chrome finish
17240/2	(2) 60W Med.	13"	5"	-	-	5 lbs.	Brushed Nickel finish
17241/1*	(1) 60W Med.	10"	10"	47"	8"	5 lbs.	Brushed Nickel finish
17242/1*	(1) 75W Med.	13"	8"	47"	-	6 lbs.	Brushed Nickel finish
17250/2	(2) 60W Med.	13"	5"	-	-	5 lbs.	Oil Rubbed Bronze finish
17251/1*	(1) 60W Med.	10"	10"	47"	8"	5 lbs.	Oil Rubbed Bronze finish
17252/1*	(1) 75W Med.	13"	8"	47"	-	6 lbs.	Oil Rubbed Bronze finish

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included



60014-1



60015-1



60004-1



60005-1



17235/1



17255/1



17245/1



HALOPHANE

Halophane glass became popular at the turn of the 20th century when it was discovered that its refractive qualities cast a crisp, even light throughout the room. These characteristics reduced shadows and allowed for a brighter and safer environment. Over a century later, we still value those same attributes. The ribbed halophane glass with complimenting turned detailing in the framework pays homage to early period lighting.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
60004-1*	(1) 150W Med.	16"	13"	-	-	12 lbs.	Polished Chrome finish
60005-1*	(1) 100W Med.	6"	10"	-	-	4 lbs.	Polished Chrome finish
60014-1*	(1) 150W Med.	16"	13"	-	-	12 lbs.	Aged Bronze finish
60015-1*	(1) 100W Med.	6"	10"	-	-	4 lbs.	Aged Bronze finish
17235/1**	(1) 100W Med.	12"	12"	50"	-	7 lbs.	Polished Chrome finish
17245/1**	(1) 100W Med.	12"	12"	50"	-	7 lbs.	Satin Nickel finish
17255/1**	(1) 100W Med.	12"	12"	50"	-	7 lbs.	Oil Rubbed Bronze finish

* (1) 6" & (2) 12" extension rods w/hang straight included

** (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included



66355/1



66345/1



66356/1



66346/1



66365/1



66375/1



66366/1



66376/1



SEAPORT

This series depicts nautical design influences with a significant solid crosshatch patterned steel cage encircling the cylindrical clear glass. Finish options include Antique Brass, Polished Chrome, Satin Nickel, and Oil Rubbed Bronze. Our optional filament bulb will add a vintage flair.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66345/1	(1) 60W Med.	6"	16"	-	7"	4 lbs.	Bulb #1092 optional, Polished Chrome finish
66346/1	(1) 60W Med.	8"	13"	-	9"	4 lbs.	Bulb #1092 optional, Polished Chrome finish
66355/1	(1) 60W Med.	6"	16"	-	7"	4 lbs.	Bulb #1092 optional, Satin Nickel finish
66356/1	(1) 60W Med.	8"	13"	-	9"	4 lbs.	Bulb #1092 optional, Satin Nickel finish
66365/1	(1) 60W Med.	6"	16"	-	7"	4 lbs.	Bulb #1092 optional, Oil Rubbed Bronze finish
66366/1	(1) 60W Med.	8"	13"	-	9"	4 lbs.	Bulb #1092 optional, Oil Rubbed Bronze finish
66375/1	(1) 60W Med.	6"	16"	-	7"	4 lbs.	Bulb #1092 optional, Antique Brass finish
66376/1	(1) 60W Med.	8"	13"	-	9"	4 lbs.	Bulb #1092 optional, Antique Brass finish



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
67045/1	(1) 60W Med.	15"	13"	53"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
67046/1	(1) 60W Med.	15"	13"	53"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
67056/1	(1) 60W Med.	15"	13"	53"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
67066/1	(1) 60W Med.	15"	13"	53"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included

* Bulb #1092 optional

WAREHOUSE PENDANT

To protect light bulbs, wire cages were used on simple metal diffusers during early factory illumination. This pendant captures the nostalgia of a by-gone era. Finished in Oil Rubbed Bronze/white, Oil Rubbed Bronze, Polished Nickel, or Satin Nickel.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
67040/1	(1) 60W Med.	10"	6"	80"	-	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
67041/1	(1) 60W Med.	10"	6"	80"	-	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze/White finish
67042/1	(1) 60W Med.	10"	6"	80"	-	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze/Chrome finish
67051/1	(1) 60W Med.	10"	6"	80"	-	2 lbs.	Includes 6 feet of clear cord, Polished Chrome/White finish

* Bulb #1092 optional

CORRINE

The Corrine pendant has a scalloped metal shade and a cast metal socket for a quaint early 20th century flair. With a variety of finish combinations, you can tailor your selection to your specific design scheme. Finish combinations include Polished Chrome and White, Oil Rubbed Bronze and White, Oil Rubbed Bronze and Chrome, and Oil Rubbed Bronze.



67060/1



67061/1



67063/1



67062/1



66370/1



66371/1



DARBY

Heat syncs are used to cool the operating temperature by dissipating heat via thin metal fins. This series captures this industrial innovation, finished in Oil Rubbed Bronze or Oil Rubbed Bronze with a white shade.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66370/1	(1) 60W Med.	16"	17"	57"	-	10 lbs.	Bulb #1099 optional
66371/1	(1) 60W Med.	16"	17"	57"	-	10 lbs.	Bulb #1099 optional
67060/1	(1) 60W Med.	4"	13"	-	4"	2 lbs.	Bulb #1102 optional
67061/1	(1) 60W Med.	5"	13"	-	5"	3 lbs.	Bulb #1102 optional
67062/1	(1) 60W Med.	6"	15"	-	7"	4 lbs.	Bulb #1102 optional
67063/1	(1) 60W Med.	5"	14"	51"	-	4 lbs.	Bulb #1102 optional



66822-1



66820-1



66823-1



66826-1



Weathered Zinc



66825-1



66800-1



Polished Chrome



66833-1



Pulldown



66827-1



Bulb #1092 optional on these fixtures



66828-1



INSULATOR GLASS

The Insulator Glass collection was inspired by the glass relics that adorned the top of telegraph lines at the turn of the 20th century. Acting as the centerpiece of this series is the recognizable shape of the glass insulator, made from thick clear glass that is complimented by solid cast hardware designed with an industrial aesthetic. Finishes include Polished Chrome, Oiled Bronze, and Weathered Zinc.



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66800-1	(1) 60W Med.	5"	8"	6"	1 lb.	Polished Chrome finish
66820-1	(1) 60W Med.	5"	8"	6"	1 lb.	
66822-1	(1) 60W Med.	9"	14"	14"	3 lbs.	
66823-1	(1) 100W Med.	7"	13"	14"	3 lbs.	
66825-1	(1) 100W Med.	7"	18"	33"	5 lbs.	Swingarm, Comes w/cord cover and plug that can be removed for direct wiring into junction box.
66826-1	(1) 60W Med.	9"	18"	34"	5 lbs.	Swingarm, Comes w/cord cover and plug that can be removed for direct wiring into junction box.
66827-1	(1) 60W Med.	9"	10"	-	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
66828-1	(1) 100W Med.	7"	10"	-	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
66833-1	(1) 60W Med.	9"	43-74"	-	6 lbs.	



66812-1



66810-1



66813-1



Oiled Bronze



66816-1



66815-1



66843-1



Pulldown



66817-1



Bulb #1092 optional on these fixtures



66818-1



INSULATOR GLASS

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66810-1	(1) 60W Med.	5"	8"	6"	1 lb.	
66812-1	(1) 60W Med.	9"	14"	14"	3 lbs.	
66813-1	(1) 100W Med.	7"	13"	14"	3 lbs.	
66815-1	(1) 100W Med.	7"	18"	33"	5 lbs.	Swingarm, Comes w/cord cover and plug that can be removed for direct wiring into junction box.
66816-1	(1) 60W Med.	9"	18"	34"	5 lbs.	Swingarm, Comes w/cord cover and plug that can be removed for direct wiring into junction box.
66817-1	(1) 60W Med.	9"	10"	-	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
66818-1	(1) 100W Med.	7"	10"	-	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
66843-1	(1) 60W Med.	9"	43-74"	-	6 lbs.	



60042-1



60043-1



60046-1



60047-1



60066-1



60045-1



60044-1



MENLOW PARK

Industrial inventions of yesteryear are reclaimed and reinterpreted to deliver the style demands of today. The classic filament style bulb can be showcased within a clear or mercury blown glass shade or proudly shown alone. An Oiled Bronze finish with a cloth cord or a Polished Chrome finish with a clear cord offer versatility for any décor.

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
60042-1	(1) 60W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60043-1	(1) 60W Med.	6"	11"	85"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60044-1	(1) 60W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60045-1	(1) 75W Med.	8"	16"	90"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60046-1	(1) 60W Med. (included)	2"	3"	77"	1 lb.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60047-1	(1) 60W Med.	6"	9"	83"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60066-1	(1) 60W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

* Bulb #1092 optional

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)





60052-1




60053-1



60056-1




60057-1



60055-1



60054-1



60065-1



Shown with light off



60064-1



Shown with light off

MENLOW PARK

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
60052-1	(1) 60W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60053-1	(1) 60W Med.	6"	11"	85"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60054-1	(1) 60W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60055-1	(1) 75W Med.	8"	16"	90"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60056-1	(1) 60W Med. (included)	2"	3"	77"	1 lb.	Includes 6 feet of clear cord, Polished Chrome finish
60057-1	(1) 60W Med.	6"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60064-1	(1) 60W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60065-1	(1) 75W Med.	8"	16"	90"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish

* Bulb #1092 optional

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)





14192/1


14191/1


14240/1


14241/1


14243/3


14190/1


14242/1



14244/6


YARDLEY

The Yardley collection features a turn of the century inspired cage design in Oil Rubbed Bronze. Optional filament bulbs will enhance its antique character.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14190/1	(1) 60W Med.	7"	11"	-	9"	2 lbs.	Bulb #1092 optional
14191/1	(1) 60W Med.	7"	11"	85"	-	2 lbs.	Includes 6 ft. of cord, Bulb #1092 optional
14192/1	(1) 60W Med.	11"	15"	67"	-	3 lbs.	Bulb #1092 optional
14240/1	(1) 60W Med.	10"	7"	45"	-	2 lbs.	Includes 6 ft. of cord, Bulb #1102 optional
14241/1	(1) 60W Med.	10"	12"	50"	-	3 lbs.	Bulb #1092 optional
14242/1	(1) 60W Med.	9"	14"	52"	-	3 lbs.	Bulb #1092 optional
14243/3	(3) 60W Cand.	16"	17"	55"	-	5 lbs.	Bulb #1101 optional
14244/6	(6) 60W Cand.	23"	26"	64"	-	7 lbs.	Bulb #1101 optional

* Please see pages 622-627 for pendant hanging options.
 (Pendants shown here for example only)





46019/1

46017/1

46014/1

46018/1

46023/1

46024/1

46007/1

46008/1

46009/1

DANICA

This collection offers scalloped glass accentuated with finely crafted stepped details on the metalwork. Choose between mercury glass with metal finished in Oiled Bronze or clear glass with metal finished in Polished Chrome.

* Please see pages 622-627 for pendant hanging options.
(Pendants shown here for example only)



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
46007/1	(1) 60W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
46008/1	(1) 60W Med.	8"	9"	83"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
46009/1	(1) 100W Med.	5"	10"	84"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
46014/1	(1) 100W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46017/1	(1) 60W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46018/1	(1) 60W Med.	8"	9"	83"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46019/1	(1) 100W Med.	5"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46023/1	(1) 50W Par 20	5"	6"	80"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
46024/1	(1) 100W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish



46221/1



46222/1



46220/1



31381/1AGS



31381/1OB



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46220/1	(1) 100W Med.	6"	16"	54"	-	3 lbs.	Bulb #1099 optional
46221/1	(1) 100W Med.	9"	15"	53"	-	4 lbs.	Bulb #1092 optional
46222/1	(1) 100W Med.	10"	14"	52"	-	4 lbs.	Bulb #1092 optional

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31381/1AGS	(1) 60W Med.	10"	17"	55"	-	4 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31381/1OB	(1) 60W Med.	10"	17"	55"	-	4 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included

B E R G E N

The Bergen collection has an eclectic combination of large, clear glass with simple metalwork finished in Oil Rubbed Bronze.

W A T E R S P H E R E

Blown water glass spheres are embellished with a spun center column. Finished in Aged Silver with Champagne glass or Oil Rubbed Bronze with Smoke glass.



See other items from this collection on page 598.



10331/1CLR
Hammered Clear



10331/1HAMB
Hammered Amber



10331/1HAQ
Hammered Aqua



10331/1HRD
Hammered Red



10431/1CLR
Hammered Clear



10431/1HAMP
Hammered Amber Plated



10431/1HAQ
Hammered Aqua



10431/1HME
Hammered Mercury



HAMMERED GLASS

This hammered glass series exudes a textural, graceful silhouette.

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10331/1HAMB	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of cord, Oil Rubbed Bronze finish
10331/1HAQ	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of cord, Oil Rubbed Bronze finish
10331/1HRD	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of cord, Oil Rubbed Bronze finish
10431/1CLR	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10431/1HAQ	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10431/1HAMP	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
10431/1HME	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

* Bulb #1092 optional

*** Please see pages 622-627
for pendant hanging options.**
(Pendants shown here for example only)





66217-1



66221-1



66210-1



66216-1



66212-2



66211-1



66213-3



Lamp arm swivels to up or down position



66214-4



QUINTON PARLOR

Inspired by chandelier glass of the Victorian period, this collection features white hand-blown glass with beautiful flutes and a leaf motif. A simple Oiled Bronze finished frame compliments the white glass adding idyllic charm.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66210-1	(1) 60W Med.	5"	12"	9"	2 lbs.	
66211-1	(1) 60W Med.	5"	12"	7"	2 lbs.	Lamp arm swivels to up or down position
66212-2	(2) 60W Med.	13"	12"	9"	4 lbs.	Lamp arm swivels to up or down position
66213-3	(3) 60W Med.	20"	12"	9"	5 lbs.	Lamp arm swivels to up or down position
66214-4	(4) 60W Med.	29"	12"	9"	7 lbs.	Lamp arm swivels to up or down position
66216-1	(1) 60W Med.	5"	25"	-	2 lbs.	Includes 3 ft. of chain
66217-1	(1) 75W Med.	11"	25"	-	5 lbs.	Includes 3 ft. of chain
66221-1	(1) 75W Med.	11"	11"	-	3 lbs.	



SCHOOLHOUSE PENDANTS

In the early 1900's, schoolhouses, banks, and other public institutions began using fully enclosed pendants that not only gave off an abundance of light, but were also easy to clean and maintain. The period authentic styling is reflected in the fluted or patterned white blown glass and matching hardware finished in Polished Chrome, Satin Nickel and Oiled Bronze. These exclusive pendants exemplify the uncompromising historic styling.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
69029-1	(1) 75W Med.	8"	12"	-	3 lbs.	Satin Nickel
69039-1	(1) 75W Med.	8"	12"	-	3 lbs.	Oiled Bronze
69040-1	(1) 150W Med.	17"	15"	-	9 lbs.	Satin Nickel
69042-1	(1) 75W Med.	8"	8"	-	3 lbs.	Satin Nickel
69043-1	(1) 75W Med.	9"	14"	-	3 lbs.	Satin Nickel
69050-1	(1) 150W Med.	17"	15"	-	9 lbs.	Oiled Bronze
69052-1	(1) 75W Med.	8"	8"	-	3 lbs.	Oiled Bronze
69053-1	(1) 75W Med.	9"	14"	-	3 lbs.	Oiled Bronze

* 1-6" and 2-12" extension rods with hang straight included



69044/1



69054/1



69045/1



69055/1



66322-4



66323-4



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
69044/1	(1) 60W Med.	9"	10"	-	-	3 lbs.	
69045/1	(1) 60W Med.	12"	12"	-	-	4 lbs.	
69054/1	(1) 60W Med.	9"	10"	-	-	3 lbs.	
69055/1	(1) 60W Med.	12"	12"	-	-	4 lbs.	

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66322-4	(3) 100W Med.	18"	24"	-	10 lbs.	Aged Bronze finish
66323-4	(4) 100W Med.	20"	25"	-	22 lbs.	Aged Bronze finish

SCHOOLHOUSE FLUSHES

In the early 1900's, schoolhouses, banks, and other public institutions began using fully enclosed ceiling fixtures that not only gave off an abundance of light, but were also easy to clean and maintain. The period authentic styling is reflected white blown glass and matching hardware finished in Satin Nickel or Oiled Bronze. These exclusive ceiling fixtures exemplify the uncompromising historic styling.

RESTORATION PENDANTS

A grouping of ceiling lighting developed with a discriminating concern for preserving historic lighting and architectural designs. This offering of expert restoration and replication fixtures is offered in a wide variety of styles and sizes.



08103-AGB



08101-AGB



08099-AGB



08097-AGB



08096-AGB



08100-AGB



RESTORATION FLUSHES

A grouping of ceiling lighting developed with a discriminating concern for preserving historic lighting and architectural designs. This offering of expert restoration and replication fixtures is offered in a wide variety of styles and sizes.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08096-AGB	(3) 75W Med.	16"	12"	-	5 lbs.	Antique Golden Bronze with Amber Antique glass
08097-AGB*	(3) 75W Med.	10"	9"	-	4 lbs.	Antique Golden Bronze with Amber Antique glass
08099-AGB	(3) 75W Med.	19"	14"	-	7 lbs.	Antique Golden Bronze with Amber Antique glass
08100-AGB*	(3) 75W Med.	12"	13"	-	3 lbs.	Antique Golden Bronze with Amber Antique glass
08101-AGB	(3) 75W Med.	16"	11"	-	5 lbs.	Antique Golden Bronze with Amber Antique glass
08103-AGB*	(3) 75W Med.	10"	10"	-	3 lbs.	Antique Golden Bronze with Amber Antique glass

* Regular medium base torpedo bulb recommended



08092-AGB



08093-AGB



66335-3



08098-AGB



08094-AGB



08095-AGB



66092-3



66093-4

RESTORATION FLUSHES

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08092-AGB*	(3) 75W Med.	12"	12"	-	3 lbs.	Antique Golden Bronze with Amber glass
08093-AGB	(4) 75W Med.	20"	13"	-	8 lbs.	Antique Golden Bronze with Amber glass
08094-AGB	(3) 75W Med.	15"	15"	-	6 lbs.	Antique Golden Bronze with Amber glass
08095-AGB	(4) 75W Med.	19"	14"	-	8 lbs.	Antique Golden Bronze with Amber glass
08098-AGB*	(3) 75W Med.	11"	10"	-	3 lbs.	Antique Golden Bronze with Frosted glass and clear highlights
66092-3*	(3) 75W Med.	12"	12"	-	3 lbs.	Dark Silver with White Antique glass
66093-4	(4) 75W Med.	20"	13"	-	10 lbs.	Dark Silver with White Antique glass
66335-3	(3) 75W Med.	12"	9"	-	3 lbs.	Oiled Bronze with Frosted glass and clear highlights

* Regular medium base torpedo bulb recommended



NORWICH

The amber restoration glass of the Norwich collection features a timeless motif that is warm and inviting. The turned center column and ironwork is complemented by an Oiled Bronze finish.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66190-1	(1) 60W Med.	8"	8"	10"	2 lbs.	
66191-3	(3) 75W Med.	14"	10"	-	5 lbs.	
66194-1	(1) 60W Med.	8"	8"	-	3 lbs.	1-6" and 2-12" extension rods with hang straight included
66195-3	(3) 100W Med.	57"	14"	16"	19 lbs.	
66196-3	(3) 60W Med.	21"	21"	-	9 lbs.	
66197-5	(5) 60W Med.	28"	20"	-	13 lbs.	



14259/5



14306/1



14305/1



14307/1

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14259/5	(5) 60W Med.	20"	16"	-	-	6 lbs.	Bulb #1092 optional

GLENDORA

Resembling an antique fan, this classically inspired semi-flush is surrounded by a Wrought Iron Black finished metalwork. Optional filament bulbs enhance the period authentic attributes.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14305/1	(1) 60W Med.	7"	18"	-	8"	3 lbs.	Bulb #1092 optional
14306/1	(1) 60W Med.	7"	13"	87"	-	3 lbs.	Bulb #1092 optional
14307/1	(1) 60W Med.	10"	18"	92"	-	4 lbs.	Bulb #1092 optional

PURCELL

The Purcell collection features genuine leather straps that suspend a steel wire cage finished in Weathered Iron.



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14300/1	(1) 60W Med.	10"	8"	82"	-	3 lbs.	
14301/3	(3) 40W Cand.	12"	11"	40"	-	5 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
14302/3	(3) 60W Med.	17"	13"	42"	-	8 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14310/1	(1) 40W Cand.	4"	9"	83"	-	2 lbs.	
14311/1	(1) 60W Med.	7"	11"	85"	-	5 lbs.	
14312/3	(3) 40W Cand.	12"	11"	49"	-	11 lbs.	

E P H R A T A

The Ephrata series offers a tapered metal drum finished in Weathered Iron with solid brass fasteners and charming handle accents.

C A F É

This collection features solid metal pendants that feature streetside café expressions precisely cut into a shade finished in Matte Black with gold accents. An eclectic addition to a breakfast nook or above a kitchen island.



14290/1



14292/3



14291/1



66945/1



66955/1

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14290/1	(1) 60W Med.	8"	12"	50"	-	3 lbs.	
14291/1	(1) 60W Med.	12"	16"	54"	-	4 lbs.	
14292/3	(3) 60W Med.	16"	20"	58"	-	7 lbs.	

STRASBURG

This collection features conically shaped metal shades finished in Weathered Iron on the outside and antique gold on the inside. Each shade has authentic riveted brass patches and a hook accent on top.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66945/1	(1) 60W Med.	10"	10"	-	14"	2 lbs.	Bulb #1092 optional
66955/1	(1) 60W Med.	10"	10"	-	14"	2 lbs.	Bulb #1092 optional

URBAN LODGE

Inspired by traditional sconce designs, these sconces update classic styles with subtle, contemporary detailing allowing greater decorating flexibility. Offered in a Weathered Bronze or Oil Rubbed Bronze finish shown with optional filament bulb.



14131/4



Shown as semi-flush



14130/1



14134/6



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
14130/1	(1) 60W Cand.	6"	12"	8"	5 lbs.	
14131/4	(4) 60W Cand.	17"	16"	-	6 lbs.	
14134/6	(6) 60W Cand.	44"	26"	18"	23 lbs.	



65004-1



65006-1



65007-5



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
65004-1	(1) 60W Cand.	12"	16"	18"	7 lbs.	
65006-1	(1) 60W Cand.	12"	18"	-	7 lbs.	
65007-5	(5) 60W Cand.	45"	25"	-	90 lbs.	

EARLY AMERICAN

The combination of wood and iron is a historic pairing of materials inspired by the early days of colonial America. Solid wood is either turned or milled to provide an understated hand-made character. The colonial maple finish compliments the Vintage Rust metalwork while the included Wheat linen shades cast a warm glow of light.

CHAPMAN

This series is reminiscent of the hurricane oil lanterns predominantly used in railroad and nautical applications in the late 1800's. Although powered by electric, the essence of this old world inspired collection remains. The Matte Black finish of the heavy ironwork cleverly contrasts the acid etched blown glass to complete the historic appeal.



14285/1



14286/2



14284/1



14282/3



14281/2



14283/4



14280/1

JONAS

This series features cast metal sockets, pipes, valve wheels, and a wood accented backplate (bath only) creating a vintage industrial expression with a multi-tone weathered finish.



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14280/1	(1) 60W Med.	5"	7"	-	7"	2 lbs.	Bulb #1092 optional
14281/2	(2) 60W Med.	12"	8"	-	6"	4 lbs.	Bulb #1092 optional
14282/3	(3) 60W Med.	19"	8"	-	6"	6 lbs.	Bulb #1092 optional
14283/4	(4) 60W Med.	26"	8"	-	6"	7 lbs.	Bulb #1092 optional
14284/1	(1) 60W Med.	8"	18"	-	8"	4 lbs.	Bulb #1092 optional
14285/1	(1) 60W Med.	2"	9"	41"	8"	3 lbs.	Bulb #1092 optional (1) 6" & (2) 12" extension rods w/hang straight included
14286/2	(2) 60W Med.	15"	7"	39"	2"	4 lbs.	Bulb #1092 optional (1) 6" & (2) 12" extension rods w/hang straight included



66265-3

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66265-3	(3) 60W Med.	20"	26"	-	12 lbs.	



1101



1102



1092



1099



1103

ITEM NO.	BULB	W	H
1092	60W Med. (240 lumens)	2.5"	5"
1099	60W Med. (240 lumens)	1.25"	7"
1101	40W Cand. (160 lumens)	1"	3.5"
1102	60W Med. (240 lumens)	1.75"	4.25"
1103	60W Med. (240 lumens)	1.25"	12"

COG AND CHAIN

Bring back the industrial age with this nostalgic pendant that features an actual chain and cogs that resemble components used on machines at the turn of the century. Finish is Vintage Rust with antique amber glass.

VINTAGE FILAMENT BULBS

These nostalgic light bulbs will enhance the look of any fixture especially those with visible bulbs.



CLASSICS

Timeless Centerpieces



ARMAND

This collection reveals an intricate laser cut pattern adorned with amber teak crystals. The crystals are designed to mimic the shape of the openings in the Weathered Bronze finished metalwork, refining the balance of the contrasting materials.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31095/1	(1) 60W Cand.	8"	9"	-	4"	2 lbs.	ADA Compliant
31096/4	(4) 60W Cand.	17"	22"	60"	-	12 lbs.	
31097/6	(6) 60W Cand.	24"	24"	62"	-	17 lbs.	
31098/6	(6) 60W Cand.	35"	18"	61"	12"	20 lbs.	



31779/6+3




Shown as semi-flush 13" H



31773/3




31778/6





Shown as semi-flush 14" H

31774/5




Shown from below



31772/1





VIVA NATURA



Brilliant arrays of crystal spears highlight the design of the Viva Natura collection. Overlapping steel wires, finished in Aged Silver, form various shapes while crystals sparkle when illuminated yet still fascinate when unlit. The combination of these elements transforms this design into a sculpture of textured light.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31772/1	(1) 60W Med.	8"	8"	46"	-	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31773/3	(3) 60W Cand.	12"	22"	60"	-	8 lbs.	
31774/5	(5) 60W Cand.	20"	9"	44"	-	13 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31778/6	(6) 60W Cand.	23"	29"	67"	-	21 lbs.	
31779/6+3	(9) 60W Cand.	30"	27"	65"	-	28 lbs.	

31770/2

31771/6

Shown as semi-flush 16" H

31780/6




(26" Corner to Corner)

31781/8




(36" Corner to Corner)

31776/6




31777/8




VIVA NATURA

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31770/2	(2) 60W Cand.	15"	8"	-	8"	4 lbs.	Pocket Sconce
31771/6	(6) 60W Cand.	18"	11"	52"	-	13 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31776/6	(6) 60W Cand.	18"	31"	73"	-	19 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31777/8	(8) 60W Cand.	25"	41"	83"	-	36 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31780/6	(6) 60W Cand.	18"	24"	68"	-	23 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31781/8	(8) 60W Cand.	25"	32"	74"	-	52 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included



VIVA NATURA

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31430/1	(1) 60W Cand.	8"	15"	-	6"	3 lbs.	
31431/3	(3) 60W Cand.	23"	11"	-	-	9 lbs.	
31432/6	(6) 60W Cand.	26"	27"	65"	-	20 lbs.	
31433/8	(8) 60W Cand.	37"	31"	69"	-	29 lbs.	



11784/7



11780/2



11783/5



11781/4




11782/5



Shown from below



11785/5+5



J A U S T E N

The Jausten collection infuses mission styling with its crystal filigree design, which is woven throughout the metalwork of the arms and basket. An Antique Bronze finish contrasts the clear crystals and highlights the unique angular design.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11780/2	(2) 60W Cand.	14"	10"	-	7"	4 lbs.	Pocket Sconce
11781/4	(4) 60W Cand.	16"	14"	-	-	7 lbs.	
11782/5	(5) 60W Cand.	21"	17"	-	-	10 lbs.	
11783/5	(5) 60W Cand.	20"	34"	73"	-	16 lbs.	
11784/7	(7) 60W Cand.	30"	43"	82"	-	29 lbs.	
11785/5+5	(10) 60W Cand.	30"	33"	72"	-	20 lbs.	



46048/6+3

46046/3

46044/4

46045/6

46047/6

46049/8+6

46040/2

EMPIRE

The Empire collection captures the regal beauty of French Empire design with its classic shape and extravagant crystal. Tapered crystal combinations gracefully flow from top to bottom via a glass bead-lined frame finished in Mocha. Unique curved crystals encircle the mid-section of the fixture creating a unique transition between the bowl and center column of each fixture.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46040/2	(2) 60W Cand.	12"	18"	-	5"	4 lbs.	
46044/4	(4) 60W Cand.	16"	11"	-	-	10 lbs.	
46045/6	(6) 60W Cand.	22"	23"	-	-	17 lbs.	
46046/3	(3) 60W Cand.	11"	23"	61"	-	10 lbs.	
46047/6	(6) 60W Cand.	16"	32"	70"	-	17 lbs.	
46048/6+3	(9) 60W Cand.	23"	42"	80"	-	31 lbs.	
46049/8+6	(14) 60W Cand.	35"	32"	70"	-	24 lbs.	



A M H E R S T

This collection showcases sparkling polished crystal weaved into an intricate wrought iron frame. The modern drum shape updates an otherwise traditional style while a rich, Antique Bronze finished frame provides the necessary contrast to allow the crystal elements to be fully recognized.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11284/2	(2) 60W Cand.	11"	11"	6"	4 lbs.	Sconce
11285/1	(1) 60W Cand.	6"	9"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
11286/4	(4) 60W Cand.	13"	10"	-	7 lbs.	
11287/6	(6) 60W Cand.	17"	8"	-	13 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
11288/6	(6) 60W Cand.	20"	29"	-	21 lbs.	
11584/1	(1) 60W Cand.	6"	9"	4"	3 lbs.	ADA Compliant
11585/2	(2) 60W Cand.	14"	5"	5"	5 lbs.	
11586/4	(4) 60W Cand.	24"	5"	5"	8 lbs.	
11587/6	(6) 60W Cand.	34"	5"	5"	11 lbs.	



Shown as semi-flush

11721/8



Shown as semi-flush

11720/6



Shown as semi-flush

11711/8



Shown as semi-flush

11710/6

VILLEGOSA

The Villegosa series features our filigree crystal in a tapered hexagonal design. Oversized rectangular crystals at each corner and metal filigree accents on top enhance this collection's elegance. Finished in Aged Silver or Spanish Bronze, these items can be hung as a pendant or mounted as a semi flush.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11710/6	(6) 60W Cand.	13"	20"	59"	-	10 lbs.	Aged Silver finish
11711/8	(8) 60W Cand.	17"	23"	62"	-	13 lbs.	Aged Silver finish
11720/6	(6) 60W Cand.	13"	20"	59"	-	10 lbs.	Spanish Bronze finish
11721/8	(8) 60W Cand.	17"	23"	62"	-	13 lbs.	Spanish Bronze finish



5967/6+4



Shown with optional shade #1023



5964/3



5970/2



5962/3



5960/1



5963/6



ELIZABETHAN

This new-age Renaissance collection graces the home with accents inspired by a moon-lit stroll along St Paul's Cathedral. The extraordinary cohesiveness of this collection captures the grandeur and grace of an era when art and architecture were as one. The captivating lines of the Dark Bronze finish accented by brilliant 32% lead crystal may adorn the grandest of settings.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
5960/1	(1) 60W Cand.	5"	12"	9"	3 lbs.	Fabric shade # 1023 optional
5962/3	(3) 60W Cand.	13"	7"	-	6 lbs.	
5963/6	(6) 60W Cand.	17"	10"	-	10 lbs.	
5964/3	(3) 60W Cand.	13"	14"	-	8 lbs.	
5967/6+4	(10) 60W Cand.	26"	29"	-	21 lbs.	Fabric shade # 1023 optional
5970/2	(2) 60W Cand.	13"	7"	6"	4 lbs.	Pocket Sconce



5972/1



Chain-hung or semi-flush adaptable



5973/4+1



5965/4



15975/8



15976/1



15974/5



15986/1



ELIZABETHAN

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
5965/4	(4) 60W Cand.	17"	27"	-	-	14 lbs.	
5972/1	(1) 60W Cand.	5"	8"	-	-	3 lbs.	(1) 6" & (2) 12" extension rods with hang straight included
5973/4+1	(5) 60W Cand.	12"	17"	-	-	9 lbs.	Chain hung or semi-flush mount adaptable
15974/5	(5) 60W Cand.	13"	13"	56"	-	11 lbs.	
15975/8	(8) 60W Cand.	17"	17"	60"	-	16 lbs.	Aged Silver finish
15976/1	(1) 60W Cand.	6"	9"	83"	-	2 lbs.	
15986/1	(1) 60W Cand.	6"	9"	83"	-	2 lbs.	



CHRISTINA

This collection displays a glamorous arrangement of filigree crystal that is carefully woven into a victorian inspired Mocha finished frame. Each line of crystal is graduated from the center to the outer edge, ending with a scalloped banding of large round faceted crystals.



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
12023/2	(2) 60W Cand.	14"	8"	8"	7 lbs.	
12024/5	(5) 60W Cand.	20"	26"	-	18 lbs.	
12025/6	(6) 60W Cand.	26"	30"	-	26 lbs.	



16240/8



16239/5



16242/1




16244/6



16243/4



Shown as semi-flush 13" H



16241/2



RENAISSANCE

Experience the re-birth of crystal! Adorned with 32% lead polished crystal, the Renaissance collection vigorously captures your spirit with an array of graceful and unexpected movements, exuding an aura of energy that radiates from a single point. The intricately carved details and our Sunset Silver finish contributes to the mystical beauty of this collection.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
16239/5	(5) 60W Cand.	13"	17"	56"	-	12 lbs.	
16240/8	(8) 60W Cand.	17"	21"	60"	-	17 lbs.	
16241/2	(2) 60W Cand.	11"	8"	-	5"	3 lbs.	Pocket Sconce
16242/1	(1) 100W Med.	6"	9"	48"	-	4 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
16243/4	(4) 60W Cand.	15"	6"	43"	-	11 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
16244/6	(6) 60W Cand.	21"	31"	70"	-	23 lbs.	



6237/6+3



6230/2



6236/6



RENAISSANCE

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
6230/2	(2) 60W Cand.	14"	13"	-	9"	4 lbs.	Fabric shade # 1058 included
6236/6	(6) 60W Cand.	28"	29"	-	-	14 lbs.	Fabric shade #1058 included
6237/6+3	(9) 60W Cand.	34"	33"	-	-	18 lbs.	Fabric shade #1058 included



6235/4



6232/4



16245/6



6231/1



6238/2



6233/6



6234/6



RENAISSANCE

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
6231/1	(1) 3-Way 100W Med.	15"	32"	-	-	7 lbs.	Shade included
6232/4	(4) 60W Cand.	16"	11"	-	-	11 lbs.	
6233/6	(6) 60W Cand.	20"	21"	-	-	19 lbs.	
6234/6	(6) 60W Cand.	20"	30"	-	-	21 lbs.	
6235/4	(4) 60W Cand.	19"	22"	-	-	9 lbs.	Fabric shade #1058 included
6238/2	(2) 60W Cand.	14"	6"	-	6"	5 lbs.	Pocket Sconce
16245/6	(6) 60W Cand.	24"	12"	-	-	23 lbs.	



Mar-a-Lago



2402/6



2400/2



2404/6+6



Shown with optional shade #1081



11000/2



Shown with optional fabric shade #1081



11001/1



SENECAL

Senecal reflects European elegance with Spanish motifs and vibrant Egyptian crystal. The graceful ironwork, crystal spheres and Spanish Bronze finish makes for a stunning collection.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2400/2	(2) 60W Cand.	14"	8"	6"	7 lbs.	Pocket sconce
2402/6	(6) 60W Cand.	20"	14"	-	12 lbs.	
2404/6+6	(12) 60W Cand.	26"	31"	-	28 lbs.	Fabric shade #1081 optional
11001/1	(1) 60W Cand.	6"	22"	-	5 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
11000/2	(2) 60W Cand.	15"	22"	7"	8 lbs.	Fabric shade #1081 optional



11696/6+3




11692/3




11693/2




11694/4




11695/8




11690/2




11691/4




ANDALUSIA

The luxuriousness of filigree crystal is unmistakable. The Andalusia collection features our glass bead-lined scrolled iron frame enhanced with shimmering crystals and an Aged Silver finish to blend with a multitude of design themes.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11690/2	(2) 60W Cand.	12"	6"	-	5"	4 lbs.	
11691/4	(4) 60W Cand.	24"	6"	-	5"	7 lbs.	
11692/3	(3) 60W Cand.	14"	31"	70"	-	8 lbs.	
11693/2	(2) 60W Cand.	13"	6"	-	-	6 lbs.	
11694/4	(4) 60W Cand.	17"	6"	-	-	10 lbs.	
11695/8	(8) 60W Cand.	24"	9"	-	-	21 lbs.	
11696/6+3	(9) 60W Cand.	28"	25"	71"	-	19 lbs.	



11705/1



11706/1



11365/1



11366/6+3

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11705/1	(1) 100W Med.	10"	16"	54"	-	4 lbs.	Aged Silver finish
11706/1	(1) 100W Med.	10"	16"	54"	-	4 lbs.	Spanish Bronze finish


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11365/1	(1) 60W Med.	19"	11"	-	10 lbs.	
11366/6+3	(9) 60W Cand.	26"	22"	-	16 lbs.	

SASHA

The Sasha pendant invokes the Victorian period with a scalloped fringe and an abundance of interlaced crystal. Choose between Aged Silver or Spanish Bronze.

LA FLOR

Inspired by the beauty and grace of a flower, this series features a multi-tiered flower shaped crystal basket with crystal accoutrements. The crystal bobeches, crystal ball topped center column, and draped crystal beading are interconnected amongst the Sunset Silver finished framework.



3345/8+4



3343/3



3341/2




3344/6

ROCHELLE

Rochelle is a magnificent collection featuring elegant amber crystal highlights, scrolling Weathered Mahogany finished ironwork and intricate castings. Incorporating elements of Renaissance design with graceful proportions, Rochelle reflects regal design and classic appeal.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
3341/2	(2) 60W Cand.	12"	18"	11"	3 lbs.	
3343/3	(3) 60W Cand.	18"	24"	-	10 lbs.	
3344/6	(6) 60W Cand.	28"	31"	-	16 lbs.	
3345/8+4	(12) 60W Cand.	42"	43"	-	52 lbs.	



2165/8+4



2166/10+5



2163/6



2161/6




2164/6+3

REGENCY

Inspired by the scrolling design of the Trump family crest, Regency creates a rich and regal ambiance. The solid cast iron scrolls and Burnt Bronze finish compliments the delicate weathered gold leaf accents and caramel amber glass to create a dramatic and stunning collection.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2161/6	(6) 60W Med.	39"	31"	22"	40 lbs.	
2163/6	(6) 60W Med.	28"	33"	-	43 lbs.	
2164/6+3	(9) 60W Med.	28"	36"	-	50 lbs.	
2165/8+4	(12) 60W Med.	36"	40"	-	76 lbs.	
2166/10+5	(15) 60W Med.	41"	48"	-	110 lbs.	



2157/3



2155/2



2154/1



2156/2



2151/2



2152/3




2153/4



2150/1

REGENCY

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2150/1	(1) 75W Med.	6"	18"	7"	5 lbs.	
2151/2	(2) 75W Med.	20"	11"	8"	7 lbs.	
2152/3	(3) 75W Med.	30"	11"	8"	10 lbs.	
2153/4	(4) 75W Med.	39"	11"	8"	12 lbs.	
2154/1	(1) 60W Med.	6"	13"	10"	3 lbs.	
2155/2	(2) 60W Med.	16"	24"	9"	11 lbs.	
2156/2	(2) 60W Med.	16"	10"	-	9 lbs.	
2157/3	(3) 60W Med.	19"	20"	-	16 lbs.	



Shown with fabric shade #1080

2493/4



2490/1



2494/6



2496/6+4



2497/6+3+6



2495/6



M I L L W O O D

Millwood reflects formal elegance and upscale design. Delicate leaf motifs and detailed ironwork compliment the distinct crystal pieces. The Antique Bronze finish with gold highlights accent the intricate detail and classic appeal of the collection.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2490/1	(1) 60W Cand.	7"	11"	5"	4 lbs.	Pocket sconce
2493/4	(4) 60W Cand.	15"	10"	-	11 lbs.	
2494/6	(6) 60W Cand.	18"	21"	-	18 lbs.	
2495/6	(6) 60W Cand.	19"	31"	-	28 lbs.	
2496/6+4	(10) 60W Cand.	25"	29"	-	23 lbs.	Fabric shade #1080 optional
2497/6+3+6	(15) 60W Cand.	29"	39"	-	35 lbs.	Fabric shade #1080 optional



GEORGIAN COURT

During the mid-eighteenth century, the Georgian style became immensely popular, not only in England, but also in Colonial America. The “Colonial” home was influenced by the Georgian style, characterized by a sense of proportion, balance, and carefully thought out details. Furniture and objects of the time were of a larger scale, yet with a lighter feeling than earlier periods. This lighter feeling transmitted grace, elegance, and prominence, and allowed details to become more of the focal point, rather than the principle elements of the structure. The Georgian Court Collection reflects those earlier influences with well-balanced proportions, attractive brass finished details, and amber glass with a marbelized finish and decorative ring.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2420/1	(1) 75W Med.	6"	15"	8"	4 lbs.	
2424/2	(2) 60W Med.	18"	12"	–	13 lbs.	
2425/3	(3) 60W Med.	21"	19"	–	15 lbs.	
2426/1	(1) 60W Med.	6"	16"	–	3 lbs.	
2431/6	(6) 60W Med.	31"	39"	–	29 lbs.	
2434/12	(12) 60W Med.	48"	62"	–	70 lbs.	



CENTRAL PARK®



3824/2



3826/5



3820/2



3825/3



3821/3



3822/4



3823/1



C H E L S E A

Chelsea integrates intricate harlequin detailing with a crystal embedded empire style framework. The clean, flowing lines, Aged Silver finish and elegant glass accents create an attractive and unique collection.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
3820/2	(2) 60W Cand.	20"	11"	8"	5 lbs.	
3821/3	(3) 60W Cand.	30"	11"	8"	7 lbs.	
3822/4	(4) 60W Cand.	39"	11"	8"	10 lbs.	
3823/1	(1) 60W Cand.	5"	19"	8"	3 lbs.	
3824/2	(2) 60W Cand.	15"	22"	10"	6 lbs.	
3825/3	(3) 60W Cand.	17"	14"	-	4 lbs.	
3826/5	(5) 60W Cand.	26"	30"	-	16 lbs.	



14006/8+4+4



14003/1



14004/1+1



14000/1+1



14005/5+5



C A M B R I D G E

The Cambridge collection combines heavy forged iron with genuine stone candle covers. When lit, the stone gives off a subtle warm glow while discreetly placed halogen lights provide the benefit of clean, functional down lighting. Finished in Moonlit Rust, this series will create a bold and historic presence.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
14000/1+1	(1) 60W Cand. (1) 50W GU10	7"	12"	7"	6 lbs.	Downlight Switch included
14003/1	(1) 60W Cand.	5"	36"	7"	6 lbs.	
14004/1+1	(1) 60W Cand. (1) 50W GU10	10"	23"	5"	4 lbs.	Downlight Switch included, (1) 6" & (2) 12" extensions rods with hang straight included
14005/5+5	(5) 60W Cand. (5) 50W GU10	33"	34"	-	43 lbs.	Downlight Switch included
14006/8+4+4	(12) 60W Cand. (4) 50W GU10	42"	44"	-	93 lbs.	Downlight Switch included



2183/6


2183/6
 Shown with optional shade #1081



2184/6+3




2181/3




2180/2


EMILION

Drawing inspiration from the creative spirit of the French Renaissance, Emilion incorporates styles indicative of the era, blending natural influences with elegant charm. The Burnt Bronze finished metalwork allows the crystal embellishments to radiate. The distinctive attributes meld together to form a compelling statement of originality.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2180/2	(2) 60W Cand.	11"	17"	8"	4 lbs.	Fabric shade #1081 optional
2181/3	(3) 60W Med.	19"	15"	-	12 lbs.	
2183/6	(6) 60W Cand.	23"	28"	-	13 lbs.	Fabric shade #1081 optional
2184/6+3	(9) 60W Cand.	32"	40"	-	19 lbs.	Fabric shade #1081 optional



11551/2



11554/1



11540/6



7958/6



7956/5



7953/2



7959/8+4



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11540/6	(6) 60W Cand.	30"	31"	71"	-	24 lbs.	
11551/2	(2) 60W Cand.	18"	27"	-	11"	10 lbs.	
11554/1	(1) 60W Cand.	11"	18"	58"	6"	4 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
7953/2	(2) 40W G9 (included)	13"	18"	6"	4 lbs.	
7956/5	(5) 40W G9 (included)	27"	13"	7"	8 lbs.	Can be mounted as a flush or sconce
7958/6	(6) 40W G9 (included)	22"	19"	-	10 lbs.	
7959/8+4	(12) 40W G9 (included)	29"	24"	-	22 lbs.	

ALLESANDRIA

The Allesandria collection features majestic open work detailing in the French Baroque style. The frame has a multi-step finish of Burnt Bronze with weathered gold leaf accents. The scalloped glass displays an elegant tapered shape with an antique amber finish.

FIORITURA

This botanical bouquet with Italian inspiration is roped neatly to provide rustic tranquility. This collection embodies juxtaposed diversity; forged iron workings in an Aged Bronze finish, offset by soft tulips that are hand-blown and hand tooled.



8050/3



8053/5



8054/5



8058/3



8056/10+5



8055/8+4



CIRCEO

The magnetic influences of this winter garden collection are the intertwined branches accented by delicately cradled crystals that resemble frozen water droplets. This collection is featured in an Antique White or Deep Rust finish.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
8050/3	(3) 60W Cand.	17"	24"	9"	5 lbs.	
8053/5	(5) 60W Cand.	21"	17"	-	7 lbs.	
8054/5	(5) 60W Cand.	27"	28"	-	9 lbs.	
8055/8+4	(12) 60W Cand.	42"	38"	-	19 lbs.	
8056/10+5	(15) 60W Cand.	54"	46"	-	26 lbs.	
8058/3	(3) 60W Cand.	16"	13"	-	5 lbs.	



18133/1




18134/4




18135/5




8059/2




8069/2




18132/3




18130/2


CIRCEO

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
8059/2	(2) 60W Med.	24"	12"	-	-	8 lbs.	
8069/2	(2) 60W Med.	24"	12"	-	-	8 lbs.	Russet Beige finish
18130/2	(2) 60W Cand.	12"	9"	-	7"	3 lbs.	Pocket sconce
18132/3	(3) 60W Med.	20"	18"	-	-	10 lbs.	
18133/1	(1) 100W Med.	10"	10"	48"	-	3 lbs.	
18134/4	(4) 60W Cand.	19"	19"	57"	-	7 lbs.	
18135/5	(5) 60W Cand.	24"	24"	63"	-	11 lbs.	



18111/2



18112/3



18113/5



18123/1



18124/4



18125/5



CIRCEO

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
18111/2	(2) 60W Med.	17"	11"	-	-	7 lbs.	
18112/3	(3) 60W Cand.	11"	12"	-	-	4 lbs.	
18113/5	(5) 60W Cand.	21"	18"	-	-	6 lbs.	
18123/1	(1) 100W Med.	10"	10"	48"	-	3 lbs.	
18124/4	(4) 60W Cand.	19"	19"	57"	-	7 lbs.	
18125/5	(5) 60W Cand.	24"	24"	63"	-	11 lbs.	



18140/2



18142/3

18141/1



18144/3



18147/8+4



18143/5



18145/5

S A G E M O R E

Inspired by the beauty of a wild cluster of vines, the Sagemore collection features crystal accented vines formed into an elegantly adaptable shape. A Bronze Rust finish offers the perfect compliment to the ample array of crystal that adorns this series.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
18140/2	(2) 60W Cand.	12"	16"	-	6"	3 lbs.	
18141/1	(1) 100W Med.	8"	9"	49"	-	2 lbs.	Bulb #1092 optional
18142/3	(3) 60W Cand.	13"	17"	55"	-	4 lbs.	
18143/5	(5) 60W Cand.	22"	26"	65"	-	9 lbs.	
18144/3	(3) 60W Cand.	15"	16"	56"	-	6 lbs.	
18145/5	(5) 60W Cand.	21"	22"	62"	-	10 lbs.	
18147/8+4	(12) 60W Cand.	37"	40"	114"	-	24 lbs.	



Shown as semi-flush 13" H




11773/8



11775/5



11777/8+4



CRYSTAL BRANCHES

This collection blends organic forms and textures with a neutral finish for versatility in a wide range of room settings. An abundance of large crystal leaves are enhanced by the nature inspired branches that are finished in Burnt Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11773/8	(8) 60W Cand.	30"	30"	68"	-	15 lbs.	
11775/5	(5) 60W Cand.	25"	17"	55"	-	7 lbs.	
11777/8+4	(12) 60W Cand.	52"	31"	105"	-	24 lbs.	



11770/2



11774/3



11771/3



11776/6+3



11772/6

CRYSTAL BRANCHES

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11770/2	(2) 60W Cand.	12"	19"	-	6"	3 lbs.	
11771/3	(3) 60W Cand.	15"	37"	-	7"	4 lbs.	
11772/6	(6) 60W Cand.	24"	8"	-	-	6 lbs.	
11774/3	(3) 60W Cand.	18"	18"	56"	-	5 lbs.	
11776/6+3	(9) 60W Cand.	33"	23"	61"	-	11 lbs.	



8090/2



8091/3



18096/3



18093/1



8092/6



18094/3



HERITAGE

This series is a tribute to England's first porcelain manufacturers dating back to the mid-18th century. Factories of the time developed product for the aristocratic market. Although many are no longer in operation, the techniques used then still apply today of hand-working molds and patterns. The strength and non-porous nature of porcelain allow intricate details and shapes as evidenced in the exquisite flowers accenting this series. This collection has crystal accents and intertwined branches finished in Cream.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
8090/2	(2) 60W Cand.	15"	18"	6"	3 lbs.	Pink porcelain roses and crystal
8091/3	(3) 60W Cand.	18"	18"	-	7 lbs.	Pink porcelain roses and crystal
8092/6	(6) 60W Cand.	22"	20"	-	10 lbs.	Pink porcelain roses and crystal
18093/1	(1) 60W Cand.	7"	12"	6"	2 lbs.	Pink porcelain roses and crystal
18094/3	(3) 60W Cand.	27"	11"	6"	4 lbs.	Pink porcelain roses and crystal
18096/3	(3) 60W Cand.	17"	8"	-	6 lbs.	Pink porcelain roses and crystal



85002



7044/3



85001



85003



85004



CRISTALLO FIORE


The Deep Rust finish of the Cristallo Fiore collection sets the backdrop for an elegant array of hand-blown glass florets. The neatly wrapped bouquet with drops of amber and clear crystal, add distinguishing design elements, indicative of Italian creativity.




ITEM NO.	BULB	W	H	WEIGHT	ADDITIONAL DETAILS
7044/3	(3) 60W Cand.	19"	13"	8 lbs.	
85001	(3) 60W Cand.	17"	18"	6 lbs.	
85002	(6) 60W Cand.	29"	26"	14 lbs.	
85003	(9) 60W Cand.	33"	31"	20 lbs.	
85004	(18) 60W Cand.	56"	81"	66 lbs.	



7043/2



7047/6



7046/3



7040/2



7042/3



7050/1



20075/3



CRISTALLO FIORE

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
7040/2	(2) 75W Med.	18"	11"	9"	7 lbs.	
7042/3	(3) 75W Med.	26"	11"	9"	10 lbs.	
7043/2	(2) 60W Cand.	14"	24"	8"	5 lbs.	
7046/3	(3) 60W Cand.	27"	12"	-	7 lbs.	
7047/6	(6) 60W Med.	38"	13"	-	17 lbs.	
7050/1	(1) 100W Med.	6"	14"	9"	3 lbs.	
20075/3	(3) 60W Cand.	30"	8"	6"	4 lbs.	

16050



86051



86052



86054




86053

H U A R C O

The true source of the Amazon was discovered in 1953 to be a small stream, The Huarco, in the Andes Mountains of Peru. The thick canopy of foliage that surrounds this meandering waterway was the inspiration for the collection. The refreshing green leaves invoke a feeling of a tropical rain forest. Complimenting the hand-blown amber glass, the base of each blossom is adorned with chestnut hues clasp clear crystal droplets.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
16050	(2) 40W G9 (included)	16"	12"	10"	3 lbs.	
86051	(3) 40W G9 (included)	16"	19"	-	5 lbs.	
86052	(3) 40W G9 (included)	23"	16"	-	6 lbs.	
86053	(6) 40W G9 (included)	28"	24"	-	12 lbs.	
86054	(8) 40W G9 (included)	28"	24"	-	13 lbs.	



9105/4



9107/4+2



9108/6+3



ITEM NO.	BULB	W	H	WEIGHT	ADDITIONAL DETAILS
9105/4	(4) 40W G9 (included)	36"	10"	19 lbs.	
9107/4+2	(6) 40W G9 (included)	32"	26"	14 lbs.	
9108/6+3	(9) 40W G9 (included)	36"	34"	24 lbs.	



20089/3



20058/2



20059/4



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
20058/2	(2) 60W Med.	14"	22"	7"	5 lbs.	Sconce
20059/4	(4) 60W Med.	22"	37"	-	19 lbs.	
20089/3	(3) 60W Med.	16"	15"	-	3 lbs.	Semi Flush



BRILLARÉ

An arrangement of multi-colored crystal florets sets a lovely theme for any décor. This collection is set apart from others with its bold, rich colors throughout, as well as vines that seem to grow naturally in various directions. Notice the crystal tips on the ends of the vines that resemble a drop of freshly fallen rain.

WINTERBERRY

The Winterberry collection offers a multitude of clear glass balls accenting the Antique Darkwood finished branches. This series has the appearance of branches covered with frozen water droplets that seemingly grow through its cream fabric shade and translucent diffuser.



4054/5



4050/2



4051/1



4052/3



4053/3



ROSAVITA

The pink rose has long been associated with poetic romance and gracefulness, but it also means light-heartedness and fun. The Rosavita collection will appeal to your love of passion and romance, as well as your playful side. Deep pink roses are complemented by light pink crystal accents and an Antique White finish.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
4050/2	(2) 60W Cand.	11"	15"	7"	2 lbs.	
4051/1	(1) 60W Med.	13"	28"	-	6 lbs.	
4052/3	(3) 60W Cand.	19"	10"	-	4 lbs.	
4053/3	(3) 60W Cand.	15"	18"	-	4 lbs.	
4054/5	(5) 60W Cand.	18"	21"	-	7 lbs.	





4000/2



4001/3

Crystal Colors



4011/3



4010/2



4003/6+3



4002/5



4012/5



4013/6+3

OPULENCE

Gorgeous collection with five crystal color options and two finishes.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
4000/2	(2) 60W Cand.	12"	15"	7"	3 lbs.	Antique White finish, shown with Rose Crystal
4001/3	(3) 60W Cand.	17"	22"	-	6 lbs.	Antique White finish, shown with Rose Crystal
4002/5	(5) 60W Cand.	20"	25"	-	9 lbs.	Antique White finish, shown with Rose Crystal
4003/6+3	(9) 60W Cand.	25"	28"	-	12 lbs.	Antique White finish, shown with Rose Crystal
4010/2	(2) 60W Cand.	12"	15"	7"	3 lbs.	Rust finish, shown with Amber Crystal
4011/3	(3) 60W Cand.	17"	22"	-	6 lbs.	Rust finish, shown with Amber Crystal
4012/5	(5) 60W Cand.	20"	25"	-	9 lbs.	Rust finish, shown with Amber Crystal
4013/6+3	(9) 60W Cand.	25"	28"	-	12 lbs.	Rust finish, shown with Amber Crystal

* Please indicate crystal color at end of item number [AMB] for Amber, [AQ] for Aqua, [CL] for Clear, [LM] for Lime, and [RS] for Rose



12008/1



12017/1



4021/1



12002/1



2391/1



2395/3



4040/3



4041/3



413-AS



2396/5



2392/2



ITEM NO.	BULB	W	H	WEIGHT	ADDITIONAL DETAILS
413-AS	(3) 60W Cand.	15"	18"	14 lbs.	Antique Silver finish, clear crystal
4021/1	(1) 60W Med.	12"	16"	5 lbs.	Rust finish, clear crystal
4040/3	(3) 60W Cand.	13"	18"	3 lbs.	Antique White finish, clear and pink crystal
4041/3	(3) 60W Cand.	13"	15"	3 lbs.	Antique White finish, clear and pink crystal
12002/1	(1) 100W Med.	10"	17"	5 lbs.	Rust finish, clear crystal
12008/1	(1) 60W Cand.	10"	16"	4 lbs.	Antique White finish, pink crystal
12017/1	(1) 60W Med.	10"	15"	3 lbs.	Antique White finish, clear crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2391/1	(1) 60W Cand.	6"	14"	10"	4 lbs.	Shades included
2392/2	(2) 60W Cand.	17"	14"	9"	4 lbs.	Shades included
2395/3	(3) 60W Cand.	20"	24"	-	8 lbs.	Shades included
2396/5	(5) 60W Cand.	23"	24"	-	12 lbs.	Shades included

ELISE

These petite chandeliers offer a waterfall of crystal accents to add a touch of class to intimate spaces.

PRINCESS

The choice of a princess for her palace, this collection exudes graceful elegance with the pristine splendor of crystal. Silk string shades and iced glass add to the palatial ambiance that radiates from this collection. Finished in Polished Chrome.



11360/9

11361/8+6



D1812



44005/6



Shown with optional shade #1091

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11360/9	(9) 60W Cand.	25"	20"	-	12 lbs.	
11361/8+6	(14) 60W Cand.	34"	38"	-	31 lbs.	Shades included

R E N E E

This elegant Empire style collection features strips of crystal beads embedded into openings in the metalwork. This creates a striking patterned effect as light passes through the lines of crystal and impart contrast to the Aged Silver metal surface. Sheer white fabric shades included.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
44005/6	(6) 60W Cand.	24"	27"	-	33 lbs.	Fabric shade #1091 optional
D1812	(1) 3-Way 150W Med.	17"	32"	-	11 lbs.	Pure white faux silk shade and fabric liner

D O N A L D S O N

This collection boasts a substantial solid clear crystal center column that is cut and polished to perfection. Hand-formed blown glass arms taper outward to hold cut crystal bobeches which is carefully complimented by metal accents finished in Polished Chrome.



11684/1



11685/1



11681/2



11680/1



11682/3



11686/6



11683/4



JAYDEN

Characterized by modern elegance, this collection features solid steel ball accents which are set among contrasting frosted reeded glass and Polished Chrome hardware.



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11680/1	(1) 100W Med.	5"	9"	-	6"	4 lbs.	
11681/2	(2) 100W Med.	13"	10"	-	6"	6 lbs.	
11682/3	(3) 100W Med.	21"	10"	-	6"	9 lbs.	
11683/4	(4) 100W Med.	29"	10"	-	6"	11 lbs.	
11684/1	(1) 100W Med.	5"	22"	-	6"	4 lbs.	
11685/1	(1) 100W Med.	5"	9"	48"	-	4 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
11686/6	(6) 100W Med.	28"	26"	65"	-	22 lbs.	



Shown as semi-flush 16" H

AUBREE

This collection offers highly polished K9 crystal beads and rectangle crystals that capture the light in an unimaginable array of sparkling beauty. The machined aluminum candle covers capture light while the Polished Nickel finish bounces the shimmering light textures among the sweeping lines.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31500/2	(2) 60W Cand.	15"	11"	-	-	10 lbs.	
31501/6	(6) 60W Cand.	23"	26"	67"	-	10 lbs.	
31502/3+3	(6) 60W Cand.	14"	27"	68"	-	17 lbs.	
31503/3	(3) 60W Cand.	11"	19"	57"	-	4 lbs.	
31504/3	(3) 60W Cand.	11"	16"	54"	-	7 lbs.	
31515/3	(3) 60W Cand.	13"	23"	61"	-	10 lbs.	



10483/5



Shown as semi-flush 24" H



10480/1



10481/3



10482/4



H A M M O N D

Clear crystals are delicately set inside individual metal rings to form a collective display of shimmering light. Finished in Polished Chrome.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
10480/1	(1) 60W Med.	7"	8"	46"	-	2 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
10481/3	(3) 60W Cand.	16"	8"	-	-	4 lbs.	
10482/4	(4) 60W Cand.	16"	11"	-	-	6 lbs.	
10483/5	(5) 60W Cand.	24"	25"	63"	-	9 lbs.	



11806/20+6+3



11805/12+6



66460/1



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11805/12+6	(6) 60W Cand. (12) 2W-1920 Lumen LED (included)	20"	21"	60"	-	14 lbs.	3500K, 85 CRI
11806/20+6+3	(9) 60W Cand. (20) 2W-3360 Lumen LED (included)	28"	30"	69"	-	25 lbs.	3500K, 85 CRI

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66460/1	(1) 60W Med.	13"	11"	51"	-	5 lbs.	Bulb #1092 optional

MANNING

A double ring of crystals are vividly highlighted by integrated LED lights which consistently illuminate the impeccable Polished Chrome metalwork, creating an exhibit of light textures.

ZUELLA

This pendant features a detailed frame in Matte Black that holds unique jewel-enhanced French-cut crystals.



31804/5




31805/5




31801/3




31802/4




31803/6


CHANDETT E

These mini chandeliers provide versatility in small settings or grouped together for a dramatic presentation above dining tables, islands and workspaces. Each possesses their own charming design pattern formed from curving metalwork. Available in an Aged Silver or Oil Rubbed Bronze finished.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31801/3	(3) 60W Cand.	14"	14"	52"	-	5 lbs.	
31802/4	(4) 60W Cand.	14"	18"	56"	-	3 lbs.	
31803/6	(6) 60W Cand.	12"	19"	57"	-	4 lbs.	
31804/5	(5) 60W Cand.	16"	24"	62"	-	5 lbs.	
31805/5	(5) 60W Cand.	15"	14"	52"	-	6 lbs.	



31814/5




31815/5




31811/3




31812/4




31813/6


CHANDETTE

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31811/3	(3) 60W Cand.	14"	14"	52"	-	5 lbs.	
31812/4	(4) 60W Cand.	14"	18"	56"	-	3 lbs.	
31813/6	(6) 60W Cand.	12"	19"	57"	-	4 lbs.	
31814/5	(5) 60W Cand.	16"	24"	62"	-	5 lbs.	
31815/5	(5) 60W Cand.	15"	14"	52"	-	6 lbs.	



Shown with optional shade #1093



15081/3



Shown as semi-flush



15083/5



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
15081/3	(3) 60W Med.	15"	16"	-	7 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
15083/5	(5) 60W Cand.	23"	23"	-	9 lbs.	Shade #1093 optional

VERONICA

With a touch of Hollywood glamour, this series blends antique mercury glass with classic design elements for a dramatic display. The contrast of the frame's Vintage Rust finish and the antique mercury glass evokes a sense of romance and charm. Optional tan linen shades add a rustic touch.



245-BK



251-BK



247-BK



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
245-BK	(5) 75W Med.	26"	24"	-	23 lbs.	
247-BK	(3) 75W Med.	40"	20"	12"	19 lbs.	
251-BK	(1) 75W Med.	10"	25"	-	7 lbs.	48" Chain

BUCKINGHAM

The Buckingham family of transitional fixtures is scaled for impact. The hand-forged iron frames have square cut arms with a Matte Black finish and white-faux marble glass shades.



15042/5



15043/6+3



15044/12+6



Shown as semi-flush



15041/3



15040/2



G L O U C E S T E R

The Gloucester collection reflects the romance of old world Europe. Finished in Weathered Bronze, this series features graceful wrought iron metalwork, candlestick styled bobeches, and a twisted center column.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
15040/2	(2) 60W Cand.	14"	18"	6"	2 lbs.	
15041/3	(3) 60W Cand.	12"	17"	-	3 lbs.	
15042/5	(5) 60W Cand.	24"	27"	-	7 lbs.	
15043/6+3	(9) 60W Cand.	36"	38"	-	11 lbs.	
15044/12+6	(18) 60W Cand.	60"	77"	-	46 lbs.	



9329/6+3



9326/3



9327/5



9319/2



9330/6+6+3



9328/5



9325/1



9321/2



9320/1



9322/3



LAWRENCEVILLE

With a casual elegance and a touch of classic styling, the Lawrenceville Collection will enhance and bring warmth to any room setting. Relaxed proportions, antique amber glass, and Mocha finish will make for an attractive, yet understated ambiance.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
9319/2	(2) 60W Med.	16"	9"	-	5 lbs.	
9320/1	(1) 75W Med.	6"	13"	7"	1 lb.	
9321/2	(2) 75W Med.	16"	10"	7"	3 lbs.	
9322/3	(3) 75W Med.	24"	10"	7"	6 lbs.	
9325/1	(1) 60W Med.	6"	19"	-	3 lbs.	
9326/3	(3) 60W Med.	17"	17"	-	7 lbs.	
9327/5	(5) 60W Med.	24"	19"	-	11 lbs.	
9328/5	(5) 60W Med.	26"	24"	-	13 lbs.	
9329/6+3	(9) 60W Med.	32"	29"	-	20 lbs.	
9330/6+6+3	(15) 60W Med.	44"	40"	-	36 lbs.	



70021-1



362-VA



363-VA



369-VA



366-VA



348-VA



TIFFANY BUCKINGHAM

The Tiffany Buckingham Collection sports our popular iron hardware and has a new stained glass design for a fashion-forward aesthetic.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
348-VA	(3) 100W Med.	54"	24"	16"	31 lbs.	
362-VA	(1) 100W Med.	16"	21"	-	12 lbs.	
363-VA	(3) 75W Med.	21"	20"	-	14 lbs.	
366-VA	(6) 75W Med.	28"	26"	-	29 lbs.	
369-VA	(1) 75W Med.	10"	25"	-	10 lbs.	48" Chain
70021-1	(1) 75W Med.	8"	11"	-	2 lbs.	

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



941-TB
[Barcode]



990-D
[Barcode]



361-VA
[Barcode]



70023-4
[Barcode]



931-VA
[Barcode]



997-AW-07
[Barcode]



999-7
[Barcode]



071-TB-07
[Barcode]



078-TB-07
[Barcode]



080-TB-07
[Barcode]



079-TB-07
[Barcode]



081-TB-07
[Barcode]

Pulldown

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
361-VA	(1) 75W Med.	8"	9"	9"	4 lbs.	Can be mounted up or down
70023-4	(4) 100W Med.	44"	18"	14"	28 lbs.	Tiffany Bronze
941-TB	(3) 75W Med.	16"	8"	-	10 lbs.	White Tiffany Glass
990-D	(2) 60W Med.	12"	5"	-	7 lbs.	Fan Kit/Ceiling Mount, White Tiffany Glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
071-TB-07	(1) 75W Med.	6"	10"	7"	5 lbs.	Tiffany Bronze finish
078-TB-07	(1) 75W Med.	6"	24"	-	5 lbs.	Tiffany Bronze finish, 18" Stem 36" Chain
079-TB-07	(1) 75W Med.	7"	12"	24"	5 lbs.	Swingarm Sconce, Tiffany Bronze finish
080-TB-07	(1) 60W Cand.	6"	13"	-	5 lbs.	Tiffany Bronze finish
081-TB-07	(1) 60W Med.	8"	40-71"	-	5 lbs.	Pulldown, Tiffany Bronze finish
931-VA	(3) 75W Med.	16"	8"	-	10 lbs.	Vintage Antique finish
997-AW-07	(3) 75W Med.	14"	16"	-	13 lbs.	Aged Walnut finish, 18" of chain per socket included
999-7	(1) 75W Med.	6"	-	-	3 lbs.	Fan Glass with 2 1/4" fitter neck

TIFFANY BUCKINGHAM

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

GRAPEVINE

Exclusive honey dune Glass is used for these traditional windowpane-style stained glass shades. "Grape" accents add color and dimension. The exclusive Vintage Antique finish has an aged patina look.

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



08018-TBH




08014-TBH




08015-TBH





70098-2




70114-1




08016-TBH


LATHAM

Inspired by an unconventional approach, this collection is noted for its high level of acceptance. Neutral colors accented by the clear water glass add to the contrast of light. Each shade is trimmed with solid brass beading and finished with Tiffany Bronze hardware with highlights.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08014-TBH	(1) 75W Med.	7"	11"	9"	4 lbs.	
08015-TBH	(3) 75W Med.	16"	15"	-	7 lbs.	
08016-TBH	(3) 60W Cand.	21"	19"	-	11 lbs.	
08018-TBH	(1) 75W Med.	7"	27"	-	5 lbs.	18" Stem 36" Chain
70098-2	(2) 60W Med.	16"	8"	8"	3 lbs.	
70114-1	(1) 75W Med.	8"	11"	-	2 lbs.	

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



078-TB-03



999-3



071-TB-03



997-AW-03



080-TB-03



035-IA



079-TB-03



Pulldown
 081-TB-03

GRAPE TRELLIS

Paneled honey-dune colored Tiffany shades are edged with a border of plump "grape" jewels. The handcrafted wrought iron frames have delicate scrolls and gilded leaves. An Iron Antique finish completes the look.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
035-IA	(5) 75W Med.	28"	18"	-	23 lbs.	Iron Antique finish
071-TB-03	(1) 75W Med.	6"	10"	7"	5 lbs.	Tiffany Bronze finish
078-TB-03	(1) 75W Med.	6"	24"	-	5 lbs.	Tiffany Bronze finish, 18" Stem 36" Chain
079-TB-03	(1) 75W Med.	7"	12"	24"	5 lbs.	Swingarm Sconce, Tiffany Bronze finish
080-TB-03	(1) 60W Cand.	6"	13"	-	5 lbs.	Tiffany Bronze finish
081-TB-03	(1) 60W Med.	8"	40-71"	-	5 lbs.	Pulldown, Tiffany Bronze finish
997-AW-03	(3) 75W Med.	14"	16"	-	13 lbs.	Aged Walnut finish, 18" of chain per socket included
999-3	(1) 75W Med.	8"	-	-	3 lbs.	Fan Glass with 2 1/4" fitter neck

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



622-AB



621-AB



08030-AB



629-AB



D1852



70113-4

FILIGREE

Making a grand statement the Filigree series offers lacey ornamental openwork composed of intertwined wire threads of brass. Each panel is hand-soldered over the glass panel to add dimensional beauty to each shade. The hardware is finished in a classic Aged Bronze to complete the majestic presentation.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08030-AB	(2) 60W Med.	14"	8"	4"	2 lbs.	Pocket Sconce ADA Compliant
621-AB	(3) 75W Med.	14"	13"	-	12 lbs.	
622-AB	(3) 100W Med.	22"	35"	-	20 lbs.	
629-AB	(1) 75W Med.	7"	39"	-	6 lbs.	18" Stem 36" Chain
70113-4	(4) 100W Med.	44"	18"	14"	28 lbs.	Tiffany Bronze
D1852	(2) 60W Med.	16"	22"	-	8 lbs.	

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



641-BC




990-J




08032-BC




70089-1




648-BC




640-BC




70165-2


DIAMOND RING

This forever lasting collection fits perfectly in just about every décor. The diamond ring pattern features oven-bent panels in hues of honey and amber which are enhanced by an exquisite blend of neutral toned stones and finished in a stately Burnished Copper.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08032-BC	(2) 60W Med.	14"	7"	4"	2 lbs.	Pocket Sconce ADA Compliant
640-BC	(3) 75W Med.	20"	15"	-	15 lbs.	
641-BC	(3) 75W Med.	16"	11"	-	10 lbs.	
648-BC	(1) 75W Med.	8"	30"	-	6 lbs.	18" Stem 36" Chain
70089-1	(1) 75W Med.	8"	11"	-	2 lbs.	
70165-2	(2) 60W Med.	16"	23"	-	9 lbs.	
990-J	(2) 60W Med.	14"	5"	-	8 lbs.	Fan Kit/Ceiling Mount

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



ENGLISH IVY

Nothing conjures an Old World feel more than English Ivy. The muted color palette of this Tiffany collection showcases an understated charm. The hardware has a Tiffany Bronze finish.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
071-TB-13	(1) 75W Med.	6"	10"	7"	5 lbs.	Tiffany Bronze finish
078-TB-13	(1) 75W Med.	6"	24"	-	5 lbs.	Tiffany Bronze finish, 18" Stem 36" Chain
079-TB-13	(1) 75W Med.	7"	12"	24"	5 lbs.	Swingarm Sconce, Tiffany Bronze finish
080-TB-13	(1) 60W Cand.	6"	13"	-	5 lbs.	Tiffany Bronze finish
081-TB-13	(1) 60W Med.	8"	40-71"	-	5 lbs.	Pulldown, Tiffany Bronze finish
715-TB	(6) 60W Cand.	20"	18"	-	21 lbs.	(1) R20 Downlight, Tiffany Bronze finish
933-TB	(3) 75W Med.	16"	8"	-	10 lbs.	Tiffany Bronze finish
997-AW-13	(3) 75W Med.	14"	16"	-	13 lbs.	Aged Walnut finish, 18" of chain per socket included
999-13	(1) 75W Med.	6"	-	-	3 lbs.	Fan Glass with 2 1/4" fitter neck

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



934-CB



614-CB



997-AW-10



071-TB-10



999-10



611-CB



080-TB-10



078-TB-10



079-TB-10



Pulldown

081-TB-10



JEWELSTONE

The Tiffany shades of the Jewelstone Collection display attractively arrayed glass in a rainbow of colors. Assembled using hundreds of vibrantly hued half-circle, square, and rectangular stained glass pieces, these portables and fixtures are true eye-catchers. Complemented in our Classic Bronze finish.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
071-TB-10	(1) 75W Med.	6"	10"	7"	5 lbs.	Tiffany Bronze finish
078-TB-10	(1) 75W Med.	6"	24"	-	5 lbs.	Tiffany Bronze finish, 18" Stem 36" Chain
079-TB-10	(1) 75W Med.	7"	12"	24"	5 lbs.	Swingarm Sconce, Tiffany Bronze finish
080-TB-10	(1) 60W Cand.	6"	13"	-	5 lbs.	Tiffany Bronze finish
081-TB-10	(1) 60W Med.	8"	40-71"	-	5 lbs.	Pulldown, Tiffany Bronze finish
611-CB	(3) 75W Med.	20"	16"	-	18 lbs.	Classic Bronze finish
614-CB	(3) 75W Med.	16"	14"	-	11 lbs.	Classic Bronze finish
934-CB	(3) 75W Med.	16"	8"	-	10 lbs.	Classic Bronze finish
997-AW-10	(3) 75W Med.	14"	16"	-	13 lbs.	Aged Walnut finish, 18" of chain per socket included
999-10	(1) 75W Med.	6"	-	-	3 lbs.	Fan Glass with 2 1/4" fitter neck

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

999-1




Size: W: 5 1/2"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-3




Size: W: 7 1/2"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-4




Size: W: 6"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-7




Size: W: 6"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-9




Size: W: 5 1/2"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-10




Size: W: 5 1/2"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-12




Size: W: 5 1/2"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-13




Size: W: 6"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-17




Size: W: 5 1/4"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-19




Size: W: 5 1/4"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-21




Size: W: 5 1/4"
Lamp: (1) 75W Med.
Weight: 3 lbs.

999-28





Size: W: 6"
Lamp: (1) 75W Med.
Weight: 3 lbs.




071-TB-01




071-TB-03




071-TB-04




071-TB-07




071-TB-09




071-TB-10




071-TB-12




071-TB-13




071-TB-17





071-TB-19




071-TB-21




071-TB-28



Tiffany Bronze Finish
Size: W: 6" H: 10" Ext: 7"
Lamp: (1) 75W Med.
Weight: 5 lbs.

MIX - N - MATCH SHADES

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

MIX - N - MATCH SHADES

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



081-TB-03
[Barcode]

081-TB-07
[Barcode]

081-TB-10
[Barcode]

081-TB-13
[Barcode]

081-TB-19
[Barcode]

081-TB-28
[Barcode]

081-TB-01
[Barcode]

081-TB-04
[Barcode]

081-TB-09
[Barcode]

081-TB-12
[Barcode]

081-TB-17
[Barcode]

081-TB-21
[Barcode]

Pulldown

Pulldown

Tiffany Bronze Finish
Size: W: 8" H: 40-71"

Lamp: (1) 60W Med.
Weight: 5 lbs.

Tiffany Bronze Finish
Size: W: 8" H: 40-71"

Lamp: (1) 60W Med.
Weight: 5 lbs.

MIX - N - MATCH SHADES

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

MIX - N - MATCH SHADES

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



72080-1



BRIMFORD



72081-1



ROSEDALE



72077-1



72078-1



72079-3



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
72080-1	(1) 60W Med.	16"	22"	-	-	8 lbs.	Zinc cast base, tiffany shade
72081-1	(1) 60W Med.	16"	22"	-	-	7 lbs.	Zinc cast base, tiffany shade

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
72077-1	(1) 60W Med.	13"	6"	-	7"	3 lbs.	Pocket Sconce
72078-1	(1) 60W Med.	13"	19"	-	-	6 lbs.	
72079-3	(2) 60W Med. (1) 60 Cand.	18"	26"	-	-	14 lbs.	

DRAGONFLY

This classic tiffany series uses a dragonfly pattern as its motif. There are multi-hued beads interlaced within the tiffany glass shade. Each lamp has a cast zinc base.



BARRINGER

The Barringer collection emulates simplicity of form and clean lines inspired by the Mission period. This was a time for craftsmen to purify over-excessive ornamentation revealing the forms that lie beneath. The warmth of tan mica shades and an Aged Bronze finish adds to its character.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
15030/2	(2) 60W Med.	14"	22"	8"	4 lbs.	
15031/3	(3) 60W Med.	13"	7"	-	4 lbs.	
15032/4	(4) 60W Med.	19"	11"	-	6 lbs.	(1) 6" and (2) 12" extension rods with hang straight included
15033/1	(1) 60W Med.	6"	19"	-	3 lbs.	(1) 6" and (2) 12" extension rods with hang straight included
15034/6	(6) 60W Med.	24"	31"	-	8 lbs.	
15035/5	(5) 60W Med.	29"	31"	-	11 lbs.	
15036/8+4	(12) 60W Med.	36"	40"	-	24 lbs.	
15037/8+8+4	(20) 60W Med.	50"	59"	-	50 lbs.	



70067-3



70065-2



70064-2



70066-1



D1849



70061-3



MICA FILIGREE

The natural beauty of genuine mica enhances decors with a rich, warm light. The Mica Filigree collection has a tan mica drum highlighted with filigree rings backed by cream tiffany glass. Finished in Tiffany Bronze, this series can coordinate nicely with classic or modern décor.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
70061-3	(3) 100W Med.	60"	14"	14"	19 lbs.	
70064-2	(2) 60W Med.	10"	6"	5"	2 lbs.	Pocket Sconce
70065-2	(2) 60W Med.	14"	9"	-	5 lbs.	
70066-1	(1) 60W Med.	6"	9"	-	2 lbs.	Includes 6 feet of cord
70067-3	(3) 60W Med.	18"	31"	-	9 lbs.	
D1849	(1) 60W Med.	14"	23"	-	8 lbs.	

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



66920/2



Shown as semi-flush 22" H



66921/8



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66920/2	(2) 60W Cand.	14"	14"	-	7"	3 lbs.	
66921/8	(8) 60W Cand.	26"	33"	74"	-	10 lbs.	

M I C A

Floral print Mica panels are set within complimenting frame designs that enhance their beauty. Finished in Weathered Bronze.



11237/1



11218/3



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11218/3	(3) 60W Med.	24"	40"	-	12 lbs.	Antique Brass finish
11237/1	(1) 60W Cand.	10"	10"	5"	2 lbs.	Pocket Sconce, Antique Brass finish

A B I N G T O N

The "pendelier" combines the attributes of a drum pendant and a chandelier. Abington was designed with classic details integrated into a transitional drum form, making it suitable for either décor.



11702/4



11700/3



Shown as semi-flush



Shown as semi-flush



11701/4

CRYSTAL SPRING

The Crystal Spring collection is graced by a fountain-like arrangement of crystals spouting from the bottom of each fixture. A cream fabric shade inside a beige organza shade diffuses a soft light, while the bottom crystal diffuser emits light that dances among the crystal. A Spanish Bronze finish on the metalwork is a luxurious compliment yet unlocks unforeseen versatility.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11700/3	(3) 60W Med.	13"	12"	47"	-	7 lbs.	(1) 2.5", (1) 6" & (2) 12" extension rods w/hang straight included
11701/4	(4) 60W Med.	23"	19"	49"	-	13 lbs.	(1) 2.5", (1) 6" & (2) 12" extension rods w/hang straight included
11702/4	(4) 60W Med.	24"	31"	70"	-	15 lbs.	



31030/1



31031/3



31033/4



31032/1



46021/3



Shown as semi-flush



46020/1



46022/4



Shown as semi-flush

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31030/1	(1) 60W Cand.	10"	10"	4"	3 lbs.	Pocket Sconce, ADA Compliant
31031/3	(3) 60W Med.	16"	13"	-	8 lbs.	
31032/1	(1) 60W Med.	7"	8"	-	3 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31033/4	(4) 60W Med.	21"	19"	-	12 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
46020/1	(1) 60W Med.	6"	10"	-	2 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
46021/3	(3) 60W Cand.	14"	21"	-	3 lbs.	
46022/4	(4) 60W Cand.	19"	28"	-	5 lbs.	

CHESTER

The distinguished metal lace pattern, finished in brushed Antique Brass, is the principle design feature which envelopes a rich cream fabric shade. A frosted amber glass diffuser completes the design while masking the direct light for a warm, ambient radiance.

CHELTHAM

The allure of the Cheltham collection is the design of the champagne plated glass which has a symmetrical ripple pattern that exudes a brilliant array of light. Further accentuating the appeal is a band of alternating champagne and clear crystals that adorn the top of the glass. The metalwork is finished in Mocha which complements the hue of the glass.



66311-3



66310-3



31396/3



31398/6

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66310-3	(3) 60W Cand.	9"	23"	-	6 lbs.	
66311-3	(3) 60W Cand.	14"	28"	-	11 lbs.	

YORKVILLE

This charming Colonial style lantern collection features clear water glass with hardware finished in Oiled Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31396/3	(3) 60W Cand.	11"	19"	57"	-	7 lbs.	
31398/6	(6) 60W Cand.	16"	23"	61"	-	13 lbs.	

FENTON

A classic lantern design is modernized with the use of slender frame rails in Oil Rubbed Bronze combined with a light amber glass.



31108/3



31109/3



22025/1



22026/3



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31108/3	(3) 60W Cand.	13"	9"	-	-	5 lbs.	
31109/3	(3) 60W Cand.	13"	9"	-	-	4 lbs.	


ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
22025/1	(1) 60W Med.	8"	15"	54"	-	5 lbs.	
22026/3	(3) 60W Cand.	14"	18"	57"	-	12 lbs.	

HELENE

The carefully strung beads dress the patterned frames of these designer flush mounts. Available in faux pearls with an Aged Silver finish or natural wood beads with an Oil Rubbed Bronze finish.

LIVERY

The Lavery pendant showcases solid Brushed Brass construction with bound clear glass panels and attractive geometric lines.



22011/3



Shown as semi-flush



22012/4



Shown as semi-flush



22013/8



22006/3



Shown as semi-flush



22005/2



Shown as semi-flush



22007/4



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
22011/3	(3) 60W Cand.	21"	6"	-	-	8 lbs.	
22012/4	(4) 60W Med.	25"	22"	61"	-	11 lbs.	
22013/8	(8) 60W Med.	43"	23"	98"	-	18 lbs.	

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
22005/2	(2) 60W Cand.	14"	6"	-	-	4 lbs.	
22006/3	(3) 60W Med.	16"	18"	57"	-	8 lbs.	
22007/4	(4) 60W Med.	24"	20"	59"	-	15 lbs.	

DECOSTAR

This series emanates an exciting star-shaped pattern with a timeless art deco flair. The design features sharp, dramatic angles made of frosted glass held by a solid Brushed Brass frame.

FRENCH DAMASK

Constructed of solid brass channeling and intricate banding in a Brushed Brass frame, this collection reveals curved glass with a beautiful damask pattern etched into each panel. The light emitted through the glass allows the pattern to become softly illuminated while casting a warm glow of light throughout the room.



Shown as semi-flush 24" H



22000/2



22003/2



22002/2



22001/6



Shown as semi-flush 17" H




22004/4




PRESTON

This English inspired design has solid Brushed Brass construction with curved frosted glass panels elegantly arranged around the perimeter. Each panel has a cast brass medallion at the center of each curved glass for a regal enhancement.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
22000/2	(2) 60W Cand.	12"	7"	-	7"	3 lbs.	Pocket Sconce
22001/6	(6) 60W Med.	23"	26"	-	-	15 lbs.	
22002/2	(2) 60W Med.	14"	6"	-	-	5 lbs.	
22003/2	(2) 60W Med.	14"	10"	49"	-	7 lbs.	
22004/4	(4) 60W Med.	18"	17"	55"	-	9 lbs.	



22016/2



22040/2



22041/8

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
22016/2	(2) 60W Med.	17"	7"	-	-	6 lbs.	Brushed Brass finish

L I N O K A

This elegant flush mount is made from solid Brushed Brass with frosted glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
22040/2	(2) 60W Med.	12"	5"	-	-	6 lbs.	
22041/8	(8) 60W Cand.	32"	17"	54"	16"	17 lbs.	

C O N L E Y

The Conley collection is made of beautifully detailed solid Brushed Brass with satin etched glass panels.



TRANSITIONAL

Understated Sophistication



63075/12



63071/2



63073/3



63074/5



63070/1



MORRISON

The Morrison collection features a warm, transitional style with an Oil Rubbed Bronze finish and wheat linen shades. The matching semi-flush offers opal white glass for ample light while highlighting the striking architectural character of the framework.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
63070/1	(1) 60W Cand.	6"	14"	-	7"	1 lb.	Shade included
63071/2	(2) 60W Med.	20"	13"	-	-	6 lbs.	
63073/3	(3) 60W Cand.	18"	20"	58"	-	4 lbs.	Shades included
63074/5	(5) 60W Cand.	26"	26"	64"	-	9 lbs.	Shades included
63075/12	(12) 60W Cand.	50"	38"	112"	-	27 lbs.	Shades included



31188/5



31185/1



31186/3



31187/4

DELANEY

The Delaney collection displays a geometric frame surrounding a single decorative bulb (sold separately) or a combination of amber glass shades. Finished in Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31185/1	(1) 60W Med.	8"	9"	83"	-	2 lbs.	Bulb #1092 optional
31186/3	(3) 60W Cand.	17"	18"	56"	-	7 lbs.	
31187/4	(4) 60W Cand.	22"	22"	60"	-	10 lbs.	
31188/5	(5) 60W Cand.	23"	26"	64"	-	11 lbs.	



46063/8



46061/3



46060/1



46062/6



VENTOUX

The Ventoux collection defines modern elegance by combining the charming characteristics of a lantern with the smooth curves of fashion forward design. Accented with crystal beads and glass candle covers, the central light cluster becomes the focal point from which crystal-lined arms are elegantly draped around. A Satin Silver finish softens the crystal for just the right balance of warmth and cutting edge style.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46060/1	(1) 60W Cand.	12"	20"	-	5"	2 lbs.	
46061/3	(3) 60W Cand.	15"	22"	60"	-	6 lbs.	
46062/6	(6) 60W Cand.	27"	40"	80"	-	13 lbs.	
46063/8	(8) 60W Cand.	44"	61"	136"	-	39 lbs.	



31474/5

31476/10



31472/3

31470/2



Shown hung with chain only



31477/1



31475/5




31473/3

MADERA

This series was designed to showcase its dramatic angles, unencumbered lines and a rich combination of a Polished Nickel frame softened with taupe finished tapered wood slats. Hanging options include all chain, or a combination of chain and rods for added sophistication.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31470/2	(2) 60W Cand.	8"	16"	-	4"	3 lbs.	ADA Compliant
31472/3*	(3) 60W Cand.	12"	18"	89"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
31473/3*	(3) 60W Cand.	12"	18"	89"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
31474/5*	(5) 60W Cand.	20"	27"	98"	-	6 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
31475/5*	(5) 60W Cand.	24"	28"	100"	-	7 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
31476/10*	(10) 60W Cand.	45"	50"	98"	-	27 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31477/1	(1) 100W Med.	12"	20"	-	12-25"	3 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box.

* Includes extension rods and chain



31337/5



31336/4




31330/1



31332/1



Shown as semi-flush



31334/3



31333/1



31331/1



31335/4



J O R G E N S O N

The Jorgenson collection stylishly bridges the gap between mid-century modern furniture design and lighting. This collection was designed using solid wood that emulates the tapered angle of fine furniture legs and angular metalwork that compliments its sleek style. Finished in taupe wood with Polished Nickel metalwork and champagne fabric shades.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31330/1	(1) 60W Cand.	6"	11"	8"	2 lbs.	
31331/1	(1) 60W Cand.	7"	24"	4"	2 lbs.	ADA Compliant
31332/1	(1) 100W Med.	10"	16"	27"	4 lbs.	Swingarm, Comes w/cord cover and plug that can be removed for direct wiring into junction box.
31333/1	(1) 75W Med.	7"	23"	-	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31334/3	(3) 60W Med.	14"	7"	-	7 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31335/4	(4) 60W Cand.	22"	11"	-	8 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31336/4	(4) 75W Med.	40"	11"	24"	11 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31337/5	(5) 60W Cand.	28"	11"	-	10 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included




31467/3+3




31466/3




Shown as semi-flush



31465/1




31457/3+3




31456/3




Shown as semi-flush



31455/1


BENICIA

This collection showcases sleek laser cut panels formed into a hexagon shape. Each panel was designed to form openings at each corner to reveal the inner hardware as well as create an interplay of outer and inner surfaces. Designer finishes include Polished Nickel and Antique Gold Leaf, both with lined glass that exude a translucent satin appearance.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31455/1	(1) 60W Cand.	7"	18"	-	4"	2 lbs.	Polished Nickel finish, ADA compliant
31456/3	(3) 60W Cand.	12"	12"	50"	-	6 lbs.	Polished Nickel finish
31457/3+3	(6) 60W Cand.	16"	24"	63"	-	14 lbs.	Polished Nickel finish
31465/1	(1) 60W Cand.	7"	18"	-	4"	2 lbs.	Antique Gold Leaf finish, ADA compliant
31466/3	(3) 60W Cand.	12"	12"	50"	-	6 lbs.	Antique Gold Leaf finish
31467/3+3	(6) 60W Cand.	16"	24"	63"	-	14 lbs.	Antique Gold Leaf finish



CENTRAL PARK®



31013/3



Shown with optional shade #1087



31007/3



31010/1



31006/5



31014/6



NEW YORK

Taking styling cues from the Art Deco period, the Trump Home® New York collection features clean lines and unique design elements. The lights are supported by rings that gracefully “float” around a larger double ring. Finished in Renaissance Silver Leaf with cream fabric shades, this series is versatile and contemporary. Shades are optional on items with crystal.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31006/5	(5) 60W Cand.	24"	24"	–	10 lbs.	Shades included
31007/3	(3) 60W Med.	16"	7"	–	10 lbs.	
31010/1	(1) 60W Cand.	6"	13"	6"	2 lbs.	Shades included
31013/3	(3) 60W Cand.	18"	20"	–	8 lbs.	Shade #1087 optional
31014/6	(6) 60W Cand.	27"	27"	–	14 lbs.	Shade #1087 optional



14205/4+4



14204/4+4



14202/2



14200/1



14201/1



14203/5



INTERSECTIONS

The Intersections collection is constructed of overlapping pieces of iron finished in Oil Rubbed Bronze. Seedy glass panels are clasped and offset, allowing reveals at the edges and enhancing its geometric style.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14200/1	(1) 60W Cand.**	10"	16"	-	6"	7 lbs.	
14201/1	(1) 60W Med.*	10"	11"	43"	-	6 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
14202/2	(2) 60W Cand.**	11"	17"	48"	-	12 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
14203/5	(5) 60W Med.*	25"	16"	49"	-	25 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
14204/4+4	(8) 60W Cand.**	17"	23"	62"	-	21 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
14205/4+4	(8) 60W Med.*	22"	30"	63"	-	35 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included

* Bulb #1100 optional

** Bulb #1101 optional



14252/4+4



14250/1

14251/3

14253/6+5

PARALLAX

Parallel and perpendicular lines intersect to create an architectural form with designer appeal. Finished in Oil Rubbed Bronze with optional filament bulbs.


ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14250/1	(1) 60W Med.	5"	21"	-	4"	2 lbs.	Bulb #1102 optional
14251/3	(3) 60W Med.	8"	21"	-	4"	2 lbs.	Bulb #1102 optional
14252/4+4	(8) 60W Med.	34"	6"	48"	9"	5 lbs.	Bulb #1102 optional, (1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
14253/6+5	(11) 60W Med.	47"	8"	48"	10"	10 lbs.	Bulb #1102 optional, (2) 6", (2) 12" & (2) 24" extension rods w/hang straight included



11436/1




11479/1

11437/2




11475/1




11438/3


ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11436/1	(1) 60W G9 (included)	5"	7"	-	6"	2 lbs.	
11437/2	(2) 60W G9 (included)	13"	7"	-	6"	4 lbs.	
11438/3	(3) 60W G9 (included)	23"	7"	-	6"	5 lbs.	
11475/1	(1) 60W G9 (included)	10"	10"	-	5"	3 lbs.	
11479/1	(1) 60W G9 (included)	4"	5"	44"	-	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included

S E R E N I T Y

Oil Rubbed Bronze finish with tan cubic glass.



31650/3




31651/3


ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31650/3	(3) 60W Med.	17"	16"	-	-	5 lbs.	
31651/3	(3) 60W Med.	22"	10"	57"	-	9 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included

S E L M A

The Selma drum fixtures have a white fabric drum shade complimented with Polished Nickel hardware and a glass diffuser recessed into the shade.



Shown from below



31262/3



31265/3



31264/3



31266/6



31260/1



31261/2



BAXTER

This series offers subtle sophistication through its unique frame design and quality details such as turned candle holders and decorative oval shaped links. Beige fabric shades combined with a Brushed Antique Brass finish to acknowledge the collection's historic attributes.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31260/1	(1) 60W Cand.	5"	11"	7"	2 lbs.	Shade included
31261/2	(2) 60W Cand.	12"	11"	7"	4 lbs.	Shades included
31262/3	(3) 60W Med.	16"	14"	-	7 lbs.	Shade included
31264/3	(3) 60W Cand.	15"	24"	-	6 lbs.	Shade included
31265/3	(3) 60W Cand.	15"	20"	-	5 lbs.	Shades included
31266/6	(6) 60W Cand.	29"	22"	-	11 lbs.	Shades included



31519/3



31529/3



Close-up of canopy



31302/1



31312/1



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31519/3	(3) 60W Med.	16"	9"	-	-	6 lbs.	
31529/3	(3) 60W Med.	16"	9"	-	-	6 lbs.	

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31302/1	(1) 75W Med.	8"	18"	-	2 lbs.	Polished Nickel finish
31312/1	(1) 75W Med.	8"	18"	-	2 lbs.	Mocha finish

CLARKTON

These semi flushes offer a clean, refined design in Oil Rubbed Bronze with a beige fabric drum shade or Aged Silver with a white fabric shade.

DALTON

The Dalton pendant's narrow body allows for ultimate functionality as an island pendant or in any area that can be accentuated by a slim design. The clear glass designer elements, above and below the fabric shade, enhance the fashionability. Choose between a white fabric shade with Polished Nickel hardware or a tan fabric shade with a Mocha finish.



10160/1



10123/6



10263/6



10162/6



10122/2



10261/2



10260/1



P E M B R O K E

Unique in form, the Pembroke collection features a concave arm design for a distinct appearance. Choose from a Polished Nickel finish with light silver drum shades or Brushed Antique Brass with light tan shades.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10122/2	(2) 60W Cand.	19"	12"	11"	3 lbs.	Shades included, Polished Nickel finish
10123/6	(6) 60W Cand.	31"	31"	-	11 lbs.	Shades included, Polished Nickel finish
10160/1	(1) 60W Med.	10"	14"	10-26"	4 lbs.	Swingarm, Shade included, Polished Nickel finish
10162/6	(6) 60W Cand.	24"	30"	-	8 lbs.	Shade included, Polished Nickel finish
10260/1	(1) 60W Med.	10"	14"	10-26"	4 lbs.	Swingarm, Shade included, Brushed Antique Brass finish
10261/2	(2) 60W Cand.	19"	12"	11"	3 lbs.	Shades included, Brushed Antique Brass finish
10263/6	(6) 60W Cand.	31"	31"	-	11 lbs.	Shades included, Brushed Antique Brass finish



31361/2



31363/3



31360/1



31370/1



31373/3



31371/2



31364/5



31362/3



31372/3



31374/5

L I L L I A N A

The Lilliana collection features fluted ceramic with a gently curving silhouette and a refined frame that will add a light and airy feel to any décor. This series is offered in two finishes including Aged Silver, seafoam ceramic and white textured linen shades, or Aged Bronze with cream ceramic and beige textured linen shades.



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31360/1	(1) 60W Cand.	6"	17"	4"	2 lbs.	ADA Compliant, shade included
31361/2	(2) 60W Med.	14"	9"	-	6 lbs.	Shade included
31362/3	(3) 60W Med.	18"	23"	-	10 lbs.	Shades included
31363/3	(3) 60W Cand.	18"	22"	-	5 lbs.	Shades included
31364/5	(5) 60W Cand.	26"	22"	-	7 lbs.	Shades included
31370/1	(1) 60W Cand.	6"	17"	4"	2 lbs.	ADA Compliant, shade included
31371/2	(2) 60W Med.	14"	9"	-	6 lbs.	Shade included
31372/3	(3) 60W Med.	18"	23"	-	10 lbs.	Shades included
31373/3	(3) 60W Cand.	18"	22"	-	5 lbs.	Shades included
31374/5	(5) 60W Cand.	26"	22"	-	7 lbs.	Shades included



61031-3



61032-5



61030-2



31225/6



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
61030-2	(2) 60W Cand.	14"	17"	6"	3 lbs.	
61031-3	(3) 60W Cand.	14"	19"	-	4 lbs.	
61032-5	(5) 60W Cand.	26"	28"	-	9 lbs.	

MEDFORD

Graceful lines and stylish symmetry are captured by the Medford collection. The character of each piece evolves with distinctively crafted wrought iron in an Oiled Bronze finish.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31225/6	(6) 60W Cand.	36"	35"	-	25 lbs.	

PORT SOLERNO

The striking characteristic of this chandelier is the seamless ring that is fabricated using separate sheets of stainless steel and polished for a sleek and clean profile. Decorative spun bobeches and a Satin Nickel finish add to the understated attributes of the piece.



10159/6+3



10120/3



10113/2



10119/3



10121/6



DIONE

The Dione collection utilizes sleek lines with laser cut oval accents to achieve a perfect balance. Finished in Polished Nickel.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10113/2	(2) 60W Cand.	15"	23"	5"	4 lbs.	Sconce
10119/3	(3) 60W Cand.	9"	17"	-	3 lbs.	
10120/3	(3) 60W Cand.	12"	26"	-	5 lbs.	
10121/6	(6) 60W Cand.	25"	31"	-	9 lbs.	
10159/6+3	(9) 60W Cand.	32"	40"	-	14 lbs.	



SCULPTIVE

This series features curvilinear Polished Chrome metal forms that compliment thick frosted textured glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11595/1	(1) 60W G9 (included)	5"	7"	-	6"	2 lbs.	
11596/2	(2) 60W G9 (included)	15"	5"	-	6"	4 lbs.	
11597/3	(3) 60W G9 (included)	22"	5"	-	6"	6 lbs.	
11598/4	(4) 60W G9 (included)	29"	5"	-	6"	7 lbs.	
11760/2	(2) 60W G9 (included)	14"	17"	-	7"	5 lbs.	Sconce
11761/3	(3) 60W G9 (included)	13"	13"	-	-	7 lbs.	
11762/1	(1) 60W G9 (included)	6"	12"	51"	-	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
11763/3	(3) 60W G9 (included)	20"	20"	65"	-	12 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
11764/6+3	(9) 60W G9 (included)	26"	21"	67"	-	18 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included



7638/6+3




7636/5




7635/3




7637/5


E L Y S B U R G

The geometric lines of this collection offer harmonious symmetry with a sophisticated contemporary appeal. This series is a perfect complement for kitchens, billiard parlors or any area that requires direct lighting. Featured in Satin Nickel with White Marbelized glass or Aged Bronze finish with Tea Stained Brown Swirl glass or white glass. Vanity also available in Polished Chrome.

ITEM NO.	BULB	W	H	WEIGHT	ADDITIONAL DETAILS
7635/3	(3) 60W Med.	20"	18"	6 lbs.	G16 1/2 bulbs recommended
7636/5	(5) 60W Med.	25"	24"	10 lbs.	G16 1/2 bulbs recommended
7637/5	(5) 60W Med.	28"	23"	9 lbs.	G16 1/2 bulbs recommended
7638/6+3	(9) 60W Med.	34"	27"	17 lbs.	G16 1/2 bulbs recommended



17047/1



7634/1



6500/1



17016/1



6501/2



6502/3

ELYSBURG

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
6500/1	(1) 75W Med.	16"	34-45"	-	9 lbs.	
6501/2	(2) 75W Med.	31"	26-38"	12"	9 lbs.	
6502/3	(3) 75W Med.	43"	26-38"	12"	11 lbs.	
7634/1	(1) 60W Med.	7"	15"	-	2 lbs.	G16 1/2 bulbs recommended
17016/1	(1) 3 Way 150W Med.	12"	17"	24"	2 lbs.	Comes w/ cord cover that can be removed for direct wiring into junction box, for use with smaller wirebox
17047/1	(1) 3-Way 150W Med.	14"	56"	22"	11 lbs.	



7631/2



7633/2



7632/3



7630/1



17019/4



7646/5



7647/5



7648/6+3



7645/3


ELYSBURG

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
7630/1	(1) 60W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended
7631/2	(2) 60W Med.	18"	8"	9"	4 lbs.	G16 1/2 bulbs recommended
7632/3	(3) 60W Med.	25"	10"	9"	5 lbs.	G16 1/2 bulbs recommended
7633/2	(2) 60W Med.	16"	15"	-	6 lbs.	G16 1/2 bulbs recommended
7645/3	(3) 60W Med.	20"	18"	-	6 lbs.	G16 1/2 bulbs recommended
7646/5	(5) 60W Med.	25"	24"	-	10 lbs.	G16 1/2 bulbs recommended
7647/5	(5) 60W Med.	28"	23"	-	9 lbs.	G16 1/2 bulbs recommended
7648/6+3	(9) 60W Med.	34"	27"	-	17 lbs.	G16 1/2 bulbs recommended
17019/4	(4) 60W Med.	36"	9"	9"	7 lbs.	G16 1/2 bulbs recommended



17027/1




7644/1




17026/1




6550/1




6551/2




6552/3


ELYSBURG

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
6550/1	(1) 75W Med.	16"	34-45"	-	9 lbs.	
6551/2	(2) 75W Med.	31"	26-38"	12"	9 lbs.	
6552/3	(3) 75W Med.	43"	26-38"	12"	11 lbs.	
7644/1	(1) 60W Med.	7"	15"	-	2 lbs.	G16 1/2 bulbs recommended
17026/1	(1) 3 Way 150W Med.	12"	17"	24"	2 lbs.	Comes w/ cord cover that can be removed for direct wiring into junction box, for use with smaller wirebox
17027/1	(1) 3-Way 150W Med.	14"	56"	22"	11 lbs.	



E L Y S B U R G

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
7640/1	(1) 60W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended, Dark Rust finish
7641/2	(2) 60W Med.	18"	8"	9"	4 lbs.	G16 1/2 bulbs recommended, Dark Rust finish
7642/3	(3) 60W Med.	25"	10"	9"	5 lbs.	G16 1/2 bulbs recommended, Dark Rust finish
7643/2	(2) 60W Med.	16"	15"	-	6 lbs.	G16 1/2 bulbs recommended, Dark Rust finish
17020/1	(1) 60W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended, Polished Chrome finish
17021/2	(2) 60W Med.	18"	8"	9"	3 lbs.	G16 1/2 bulbs recommended, Polished Chrome finish
17023/3	(3) 60W Med.	25"	10"	9"	5 lbs.	G16 1/2 bulbs recommended, Polished Chrome finish
17024/4	(4) 60W Med.	36"	9"	9"	7 lbs.	G16 1/2 bulbs recommended, Polished Chrome finish
17029/4	(4) 60W Med.	36"	9"	9"	7 lbs.	G16 1/2 bulbs recommended, Dark Rust finish



17648/6+3




17646/5




17645/3




17647/5



ELYSBURG

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17645/3	(3) 60W Med.	20"	18"	92"	-	6 lbs.	G16 1/2 bulbs recommended
17646/5	(5) 60W Med.	25"	24"	98"	-	10 lbs.	G16 1/2 bulbs recommended
17647/5	(5) 60W Med.	28"	23"	97"	-	9 lbs.	G16 1/2 bulbs recommended
17648/6+3	(9) 60W Med.	34"	27"	101"	-	17 lbs.	G16 1/2 bulbs recommended



16551/2


17644/1

16550/1




16552/3




17641/2




1743/2




17642/3





17640/1




17643/4


ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
1743/2	(2) 60W Med.	16"	15"	-	-	6 lbs.	G16 1/2 bulbs recommended
16550/1	(1) 75W Med.	16"	34-45"	-	-	9 lbs.	
16551/2	(2) 75W Med.	31"	26-38"	-	12"	9 lbs.	
16552/3	(3) 75W Med.	43"	26-38"	-	12"	11 lbs.	
17640/1	(1) 60W Med.	7"	12"	-	8"	2 lbs.	G16 1/2 bulbs recommended
17641/2	(2) 60W Med.	18"	8"	-	9"	4 lbs.	G16 1/2 bulbs recommended
17642/3	(3) 60W Med.	25"	10"	-	9"	5 lbs.	G16 1/2 bulbs recommended
17643/4	(4) 60W Med.	36"	9"	-	9"	7 lbs.	G16 1/2 bulbs recommended
17644/1	(1) 60W Med.	7"	15"	89"	-	2 lbs.	G16 1/2 bulbs recommended

ELYSBURG



20150/1

20152/3



20151/2



20155/6




20154/6

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
20150/1	(1) 60W Cand.	6"	13"	7"	2 lbs.	Shade included
20151/2	(2) 60W Cand.	15"	14"	5"	4 lbs.	
20152/3	(3) 60W Med.	18"	12"		8 lbs.	
20154/6	(6) 60W Cand.	22"	24"		12 lbs.	
20155/6	(6) 60W Cand.	28"	23"		10 lbs.	Shades included

SEVEN SPRINGS

From the Trump Home® Central Park collection, Seven Springs displays fine workmanship throughout with its seamlessly crafted L-shaped arms, solid metal turnings, and a Satin Nickel finish. Cream fabric drum shades are included.



1624/6



1620/2

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1620/2	(2) 60W Cand.	13"	19"	9"	3 lbs.	Shades included
1624/6	(6) 60W Cand.	24"	29"	-	17 lbs.	

TRIBECA

Tribeca creates a sophisticated, modern appeal with a Polished Nickel finish, cream colored glass and cream hardback fabric shades. Inspired by the Manhattan lifestyle, Tribeca combines downtown chic with timeless elegance.





Shown as semi-flush

Shown as semi-flush

CHANDLER

This series features a crosshatch patterned glass that exudes dazzling light textures. The glass is held by a heavy metal frame with stepped rings to further enrich the distinction of the design. Choose between Polished Nickel with clear glass or Oil Rubbed Bronze with champagne glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31450/1	(1) 60W Cand.	6"	14"	-	5"	4 lbs.	Oil Rubbed Bronze finish
31451/3	(3) 60W Cand.	11"	8"	51"	-	8 lbs.	Oil Rubbed Bronze finish
31452/4	(4) 60W Cand.	18"	12"	56"	-	14 lbs.	Oil Rubbed Bronze finish
31453/8	(8) 60W Cand.	18"	24"	69"	-	28 lbs.	Oil Rubbed Bronze finish
31460/1	(1) 60W Cand.	6"	14"	-	5"	4 lbs.	Polished Nickel finish
31461/3	(3) 60W Cand.	11"	8"	51"	-	8 lbs.	Polished Nickel finish
31462/4	(4) 60W Cand.	18"	12"	56"	-	14 lbs.	Polished Nickel finish
31463/8	(8) 60W Cand.	18"	24"	69"	-	28 lbs.	Polished Nickel finish



20007/3



20008/3



20005/1



20009/5



20006/5



ALEXIS

With a bold, metropolitan style, the Alexis collection exudes glamour and sophistication. Blown cracked glass spheres are highlighted by a soft light that passes through the translucent silver shades, while an Antique Silver frame enhances its graceful allure.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
20005/1	(1) 60W Cand.	7"	15"	4"	2 lbs.	Sconce ADA Compliant
20006/5	(5) 60W Med.	23"	12"	-	11 lbs.	
20007/3	(3) 60W Med.	18"	28"	-	9 lbs.	
20008/3	(3) 60W Med.	25"	26"	-	8 lbs.	
20009/5	(5) 60W Med.	32"	27"	-	17 lbs.	



57026/1




57027/4





57025/2




31122/3




31123/1




31120/1




31127/5




31121/2


ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
57025/2	(2) 60W Med.	13"	6"	-	-	5 lbs.	
57026/1	(1) 100W Med.	6"	8"	52"	-	3 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
57027/4	(4) 100W Med.	24"	25"	63"	-	10 lbs.	

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31120/1	(1) 60W Cand.	5"	19"	4"	2 lbs.	ADA Compliant, shade included
31121/2	(2) 60W Cand.	20"	18"	4"	3 lbs.	ADA Compliant, shade included
31122/3	(3) 60W Med.	16"	13"	-	11 lbs.	
31123/1	(1) 60W Med.	6"	11"	-	4 lbs.	
31127/5	(5) 60W Med.	25"	22"	-	7 lbs.	Shades included

D I F F U S I O N

The centerpiece of this collection is the antique charm of mercury glass that is modernized through a softly diffusing beige organza drum shade. The clean and simplistic Oil Rubbed Bronze finished metalwork supplies a striking contrast to the lighter colored shades.

E S T O N I A

Inspired from a historic architectural design motif, the overlapping pattern is used in a variety of ways to properly balance each piece in the collection. The series has a rich Aged Silver finish and beige fabric shades for a quintessential modern-traditionalist style.



Shown as semi-flush 14" H



SANTA MONICA

The Santa Monica collection features classic design elements demonstrated by the fleur de lis accented chain and laser cut metalwork. Conversely, a champagne fabric shade with a frosted glass diffuser and Aged Silver finish contribute to a more updated sensibility.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31426/1	(1) 60W G9 (included)	6"	9"	-	4"	2 lbs.	ADA compliant
31427/2	(2) 60W G9 (included)	16"	6"	-	4"	4 lbs.	
31428/3	(3) 60W G9 (included)	23"	6"	-	4"	5 lbs.	
31429/4	(4) 60W G9 (included)	30"	6"	-	4"	6 lbs.	
31523/3	(3) 60W Med.	18"	6"	50"	-	10 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31524/5	(5) 60W Med.	24"	28"	51"	-	15 lbs.	
31525/4	(4) 60W Med.	32"	7"	65"	9"	15 lbs.	



72000-2



72001-1



72003-3



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
72000-2	(2) 60W Cand.	10"	6"	5"	3 lbs.	Pocket Sconce
72001-1	(1) 60W Med.	7"	10"	-	3 lbs.	Includes 6 Feet of Cord
72003-3	(3) 60W Med.	16"	11"	-	7 lbs.	

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

CIRQUE

The Cirque collection features an updated style using round tiffany glass pieces arranged into drum shapes. Finished in Matte Black, this series combines modern functionality with the warmth and beauty of tiffany.



002-TS



001-TS



001-AB



002-AB



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
001-AB	(1) 100W Med.	16"	18"	8"	9 lbs.	Antique Bronze finish
001-TS	(1) 100W Med.	16"	18"	8"	9 lbs.	Tarnished Silver finish
002-AB	(1) 100W Med.	16"	38"	8"	12 lbs.	Antique Bronze finish, includes portable plug kit
002-TS	(1) 100W Med.	16"	38"	8"	12 lbs.	Tarnished Silver finish, includes portable plug kit

AURORA


Warm yet contemporary, this collection boasts gracefully sculptured metalwork. The Antique Bronze finish is paired with Amber Scavo glass for a soft effect, while the Tarnished Silver finish is complemented by white faux-alabaster glass.



10413/4




10411/3





Shown as semi-flush 17" H




10412/1
 Multi Shells





10415/1
 Multi Bunched Shells




10416/1
 Multi Bunched Shells




10414/1
 Ribbed Shells

10380/1





10370/1


SHELLS

This naturally inspired shell collection will bring a sense of tranquility with its naturally toned shells that artfully capture the light. Hardware is finished in Satin Nickel.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
10370/1	(1) 60W Med.	12"	6"	-	3"	3 lbs.	Pocket Sconce, ADA Compliant
10380/1	(1) 60W Med.	12"	6"	-	3"	2 lbs.	Pocket Sconce, ADA Compliant
10411/3	(3) 60W Med.	16"	8"	-	-	6 lbs.	
10412/1	(1) 60W Med.	5"	7"	81"	-	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10413/4	(4) 60W Med.	20"	18"	56"	-	11 lbs.	
10414/1	(1) 60W Med.	6"	8"	82"	-	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10415/1	(1) 60W Med.	6"	8"	82"	-	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10416/1	(1) 60W Med.	6"	8"	82"	-	3 lbs.	Includes 6 feet of white cord, Matte White finish

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)





10272/4



10271/3



10270/2



10281/3



10280/2



10282/4



LUMINESE

The sparkling effect of the glass in this series is captivating. The process to achieve this desired result starts with making a clear, hand-formed glass bowl. Then, a coating of either clear or amber mini glass fragments are melted to the inside surface, giving it a crystallized appearance, while the outside surface remains smooth. Choose between a Satin Nickel frame with clear glass or Aged Bronze frame with amber glass.



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10270/2	(2) 40W G9 (included)	7"	14"	3"	4 lbs.	Pocket Sconce, ADA Compliant
10271/3	(3) 60W Med.	16"	8"	-	9 lbs.	
10272/4	(4) 60W Med.	24"	25"	-	21 lbs.	
10280/2	(2) 40W G9 (included)	7"	14"	3"	4 lbs.	Pocket Sconce, ADA Compliant
10281/3	(3) 60W Med.	16"	8"	-	9 lbs.	
10282/4	(4) 60W Med.	24"	25"	-	21 lbs.	




10420/4




Shown as semi-flush 17" H



10418/3



10419/1
 Multi



10371/1



10429/1
 Fuschia

GLASS MOSAIC

Pieces of thick glass are assembled into a unique mosaic that exude a soft, rich light. Fuschia or Multi colored glass combines with a Satin Nickel finish for an updated look.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
10371/1	(1) 60W Med.	12"	6"	-	3"	3 lbs.	Pocket Sconce, ADA Compliant
10418/3	(3) 60W Med.	16"	8"	-	-	11 lbs.	
10419/1	(1) 60W Med.	5"	7"	81"	-	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10420/4	(4) 60W Med.	20"	18"	56"	-	17 lbs.	
10429/1	(1) 60W Med.	5"	7"	81"	-	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish

*** Please see pages 622-627 for pendant hanging options.**
 (Pendants shown here for example only)



73023-5



AVALON

This series showcases hand-painted crackled glass with colorful textured patterns and hardware finished in Satin Nickel.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
73011-1	(1) 60W Med.	5"	8"	-	2 lbs.	Includes 6 feet of clear cord
73020-2	(2) 60W Cand.	7"	15"	3"	3 lbs.	Sconce, ADA Compliant
73021-1	(1) 60W Med.	5"	8"	-	2 lbs.	Includes 6 feet of clear cord
73022-3	(3) 60W Med.	16"	11"	-	6 lbs.	
73023-5	(5) 60W Med.	24"	24"	-	7 lbs.	
73030-2	(2) 60W Cand.	7"	15"	3"	3 lbs.	Sconce, ADA Compliant
73031-1	(1) 60W Med.	5"	8"	-	2 lbs.	Includes 6 feet of clear cord
73032-3	(3) 60W Med.	16"	11"	-	6 lbs.	
73033-5	(5) 60W Med.	24"	24"	-	7 lbs.	
73041-1	(1) 60W Med.	5"	8"	-	2 lbs.	Includes 6 feet of clear cord



70046-1



70048-4 shown with shortened stem (included)



70044-2



Glass shown with light off



70048-4



19000/1



19003/6



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
70044-2	(2) 60W Cand.	9"	12"	5"	3 lbs.	Pocket Sconce
70046-1	(1) 60W Med.	6"	9"	-	3 lbs.	Includes 6 feet of cord
70048-4	(4) 60W Med.	22"	35"	-	12 lbs.	

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
19000/1	(1) 60W Med.	9"	16"	-	13 lbs.	Aged Bronze finish
19003/6	(6) 60W Med.	26"	25"	-	28 lbs.	Aged Bronze finish

D I M E N S I O N S

The Dimensions collection incorporates modern lines with bold proportions. Panels of glass are slumped and arranged into a unique three-dimensional geometric pattern. Finished in Burnished Copper, this collection comes with tea stained glass.

S P A N I S H M O S A I C

Old world meets transitional styling in the Spanish Mosaic collection. Genuine alabaster is hand-cut and carefully pieced together. The mosaic pattern created by the intersection of the alabaster pieces contribute to the design and character.



9025/6

ITEM NO.	BULB	W	H	WEIGHT	ADDITIONAL DETAILS
9025/6	(6) 60W Med.	24"	29"	20 lbs.	

MARBLLED STONE

Give your room an upscale look with this genuine stone pendant. This fixture is carved into a solid piece of stone with a beautiful texture and veining that only nature can provide. This pendant features a rose tea leaf hue set on a Matte Nickel frame.



8820/8

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
8820/8	(8) 60W Med.	24"	18"	-	15 lbs.	Chain hung or semi-flush mount adaptable

STONE MOSAIC

Translucent quartz stone is carved and pieced together to form attractive mosaics. Each stone comes to life when illuminated. Dark Antique Brass suspensions cradle the mosaic bowls for a refined elegance.



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
8884/2	(2) 60W Cand.	12"	6"	6"	5 lbs.	Pocket sconce
8887/6	(6) 60W Med.	24"	23"	-	20 lbs.	
8888/8	(8) 60W Med.	32"	27"	-	34 lbs.	
8889/2	(2) 60W Med.	12"	6"	-	5 lbs.	Semi flush

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
9003/2	(2) 60W Cand.	17"	10"	6"	6 lbs.	Pocket sconce
9010/9	(9) 60W Med.	39"	38"	-	60 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included

STONYBROOK

Weathered by time and the graceful ebb of a tranquil stream, the Stonybrook collection gathers these stones together to form handsome, lens-shaped bowls in pearl-hued stone with a Satin Nickel frame.

IMPERIAL GRANITE

Enhance the beauty of your home with the timeless beauty of genuine stone. These stunningly spectacular fixtures feature stone with signature random veining and casts a warm and natural hue of light. Each fixture is supported by a solid Antique Brass frame that will stand the test of time.



MODERN
Leading Edge Designs



31571/12



31570/8



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31570/8	(8) 50W GU10	21"	44"	129"	-	25 lbs.	
31571/12	(12) 50W GU10	32"	67"	152"	-	43 lbs.	

LINKS

This collection uses laser cut Polished Stainless Steel to form spectacular angular links that suspend from an oversized custom chain. This suspended work of art has strategically placed recessed MR16 bulbs that highlight the impeccable surfaces of the sculpture.



31018/6



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31018/6	(6) 60W Cand.	24"	24"	68"	-	14 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

CRESTWOOD

A dynamic combination of solid wood and metal form the unified outer rings of the Crestwood fixture. At its core, a champagne fabric drum shade provides a soft glow against the Polished Nickel finished metalwork and the Chestnut wood finish.



31556/6



Shown at varying heights with included extension rods



31550/1



31551/3



31554/1



31555/3


J A N E T T E

The Janette collection has an updated mid-century style that combines clean lines with warm wood tones. Chestnut finished wood slats add a natural element and soft contrast to the Polished Nickel finished hardware.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31550/1	(1) 60W Med.	7"	29-53"	-	10"	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31551/3	(3) 60W Med.	19"	8"	-	-	8 lbs.	
31554/1	(1) 60W Med.	7"	16"	61"	-	3 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31555/3	(3) 60W Med.	14"	31"	76"	-	7 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
31556/6	(6) 60W Med.	19"	43"	88"	-	16 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

* Bulb #1092 optional



66940/1


66941/4

 (25" Corner to Corner)

Translucent Mica



66930/1


66931/4

 (25" Corner to Corner)

Marble Printed Mica

M I C A

Mica panels are set within complimenting frame designs that enhance their beauty. Finished in Oil Rubbed Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66930/1	(1) 60W Cand.	8"	11"	-	5"	2 lbs.	
66931/4	(4) 60W Cand.	18"	25"	64"	-	9 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
66940/1	(1) 60W Cand.	8"	11"	-	5"	2 lbs.	
66941/4	(4) 60W Cand.	18"	25"	64"	-	9 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included



66950/1



66951/3



Tan Mica

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
66950/1	(1) 60W Cand.	7"	9"	-	4"	2 lbs.	ADA Compliant
66951/3	(3) 60W Med.	20"	32"	71"	-	9 lbs.	

M I C A



14051/3



14050/1



14052/6



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
14050/1	(1) 60W Med.	14"	16"	9"	7 lbs.	Pocket Sconce
14051/3	(3) 60W Med.	19"	17"	-	12 lbs.	
14052/6	(6) 60W Med.	26"	22"	-	19 lbs.	

C U M B E R L A N D

An outer drum made of criss-crossing iron finished in Classic Bronze encloses a light amber organza diffuser. An additional layering element is the matching finished mini-chandelier, within the fixture, that is properly accented with frosted blown glass shades.



57092/4+4




57091/4




57094/8




57090/1




57093/5


LINDHURST

The Lindhurst collection reveals a light, airy design augmented with mercury glass panels elegantly suspended from custom designed hooks. The slender lines are highlighted by the Oil Rubbed Bronze finish which, with its neutral attributes, can coordinate with a wide range of decors.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
57090/1	(1) 60W Cand.	4"	13"	-	4"	3 lbs.	ADA Compliant
57091/4	(4) 60W Cand.	21"	8"	-	-	8 lbs.	
57092/4+4	(8) 60W Cand.	16"	22"	61"	-	18 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
57093/5	(5) 60W Cand.	33"	11"	56"	8"	15 lbs.	(2) 6", (2) 12" & (2) 24" extension rods w/hang straight included
57094/8	(8) 60W Cand.	22"	11"	56"	-	15 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

* Bulb #1101 optional on all above



72071-2



72072-1



72070-2



72061-2



72062-1



72063-4



72060-2



CUBIST

Cubes of tiffany glass are assembled into a structure of offsetting staggered cubes, creating an innovative textural expression. With hardware finished in Brushed Nickel, this series comes with a choice of white or limited edition dusk sky tiffany glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
72060-2	(2) 60W Cand.	7"	10"	-	5"	3 lbs.	
72061-2	(2) 60W Med.	13"	11"	-	-	7 lbs.	
72062-1	(1) 60W Med.	6"	9"	41"	5"	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
72063-4	(4) 60W Med.	27"	9"	53"	8"	13 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
72070-2	(2) 60W Cand.	7"	10"	-	5"	3 lbs.	
72071-2	(2) 60W Med.	13"	11"	-	-	7 lbs.	
72072-1	(1) 60W Med.	6"	9"	41"	5"	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
72073-4	(4) 60W Med.	27"	9"	53"	8"	13 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
14120/1	(1) 60W Cand.	7"	12"	6"	3 lbs.	
14121/1	(1) 100W Med.	7"	8"	-	4 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
14122/4	(4) 60W Cand.	18"	18"	-	14 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
14123/6	(6) 60W Cand.	24"	24"	-	26 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
72021-1	(1) 60W Med.	7"	11"	-	4 lbs.	Includes 6 feet of clear cord
72022-3	(3) 60W Med.	16"	10"	-	8 lbs.	1-6" and 2-12" extension rods with hang straight included

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

CUBIX

The Cubix collection features an exciting "cube in cube" design, with the outer cube suspending the inner cube of clear water glass panels that are the centerpiece of the design. The complimenting, Oiled Bronze finish is adaptable to a variety of style settings.

TETRA

The Tetra collection represents a modern approach to tiffany. Using triangular cut pieces of white tiffany glass, each fixture is assembled using triangles, to create visually pleasing geometric shapes. Polished Chrome hardware enhances its updated appeal.



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
14270/1	(1) 60W Med.	16"	14"	88"	-	3 lbs.	Bulb #1103 optional
14271/1	(1) 60W Med.	16"	14"	88"	-	3 lbs.	Bulb #1103 optional
14272/1	(1) 60W Med.	15"	14"	87"	-	3 lbs.	Bulb #1103 optional
14273/1	(1) 60W Med.	18"	18"	92"	-	5 lbs.	Bulb #1099 optional

GEOWEB

This series features layered geometric shapes to form an intricate webbed design. Finished in Urban Concrete and shown with an optional filament bulb.



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17190/1	(1) 100W Med.	12"	13"	87"	-	2 lbs.	


ROXA

Etched stainless steel mini pendant with Polished Chrome hardware.



H A M M E R S M I T H

A free-form hammered surface gives the Polished Chrome or Copper finishes a textural metallic shimmer. This collection of pendants offers unique shapes for use within a wide range of decors.



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46200/1	(1) 60W Med.	5"	9"	82"	-	2 lbs.	Includes 6 feet of clear cord
46201/1	(1) 100W Med.	10"	10"	84"	-	2 lbs.	Includes 6 feet of clear cord
46202/1	(1) 100W Med.	16"	9"	83"	-	4 lbs.	Includes 6 feet of clear cord
46203/1	(1) 100W Med.	8"	18"	92"	-	3 lbs.	Includes 6 feet of clear cord
46210/1	(1) 60W Med.	5"	9"	82"	-	2 lbs.	Includes 6 feet of clear cord
46211/1	(1) 100W Med.	10"	10"	84"	-	2 lbs.	Includes 6 feet of clear cord
46212/1	(1) 100W Med.	16"	9"	83"	-	4 lbs.	Includes 6 feet of clear cord
46213/1	(1) 100W Med.	8"	18"	92"	-	3 lbs.	Includes 6 feet of clear cord



LED



REILLY

The Reilly collection features adjustable LED technology that offers crisp illumination and versatility among sleek modern lines. The light holder is made of solid brushed aluminum while the framework is done in a complimentary Brushed Nickel finish.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
54010/1	(1) 5W-450 Lumen LED (integrated)	5"	7"	-	6"	1 lb.	3000K, 80 CRI
54011/2	(2) 5W-450 Lumen LED (integrated)	14"	5"	-	8"	1 lb.	3000K, 80 CRI
54012/3	(3) 5W-450 Lumen LED (integrated)	22"	5"	-	8"	2 lbs.	3000K, 80 CRI
54013/4	(4) 5W-450 Lumen LED (integrated)	8"	6"	-	8"	3 lbs.	3000K, 80 CRI, Dimmable
54014/1	(1) 5W-450 Lumen LED (integrated)	10"	56"	-	21"	7 lbs.	3000K, 80 CRI, Switch on tube
54015/3	(3) 5W-450 Lumen LED (integrated)	9"	63"	-	-	8 lbs.	3000K, 80 CRI
54016/4	(4) 5W-450 Lumen LED (integrated)	14"	4"	78"	11"	4 lbs.	3000K, 80 CRI, Dimmable
54017/6	(6) 5W-450 Lumen LED (integrated)	24"	4"	78"	11"	5 lbs.	3000K, 80 CRI, Dimmable
54018/1	(1) 5W-450 Lumen LED (integrated)	5"	5"	-	16-28"	3 lbs.	3000K, 80 CRI



50003/LED



LED

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
50003/LED	12W-1200 Lumen LED (integrated)	39"	2"	76"	3"	5 lbs.	3000K, 80 CRI

L I N O

Lino is a linear LED light fixture, finished in Matte Black, that will enhance an island or dining room table with its slim design and crisp, functional light.



17170/1



17171/3



LED

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17170/1	(1) 5W-700 Lumen LED (included)	4"	9"	82"	-	1 lb.	3200K, 80 CRI
17171/3	(3) 5W-2100 Lumen LED (included)	20"	9"	83"	3"	4 lbs.	3200K, 80 CRI

V A S S O C H R O M O

This unique wine glass inspired pendant has graceful curves, made of steel, and unencumbered lines which are accentuated with a Polished Chrome finish and integrated LED lighting.



L I N D S E Y

This mini pendant collection features a smooth flowing shape from the canopy to the teardrop body. The Brushed Nickel finish adds beautiful contrast to all of the curvaceous pendant bodies, including stylish wood prints.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31341/1BW	(1) 100W Med.	6"	14"	-	-	2 lbs.	Includes 6 feet of clear cord
31341/1OB	(1) 100W Med.	6"	14"	-	-	2 lbs.	Includes 6 feet of clear cord
31341/1SN	(1) 100W Med.	6"	14"	-	-	2 lbs.	Includes 6 feet of clear cord
31442/1BW	(1) 100W Med.	17"	16"	95"	-	2 lbs.	Includes 6 feet of clear cord
31442/1DW	(1) 100W Med.	17"	16"	95"	-	2 lbs.	Includes 6 feet of clear cord
31442/1MO	(1) 100W Med.	17"	16"	95"	-	2 lbs.	Includes 6 feet of clear cord
31442/1SN	(1) 100W Med.	17"	16"	95"	-	2 lbs.	Includes 6 feet of clear cord



31340/1MO
Medium Oak



31340/1SN
Satin Nickel



31340/1BW
Burl Wood



31340/1OB
Oiled Bronze




31340/1DW
Darl Walnut



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31340/1BW	(1) 50W GU10 (included)	4"	10"	-	1 lb.	Includes 6 feet of clear cord
31340/1DW	(1) 50W GU10 (included)	4"	10"	-	1 lb.	Includes 6 feet of clear cord
31340/1MO	(1) 50W GU10 (included)	4"	10"	-	1 lb.	Includes 6 feet of clear cord
31340/1OB	(1) 50W GU10 (included)	4"	10"	-	1 lb.	Includes 6 feet of clear cord
31340/1SN	(1) 50W GU10 (included)	4"	10"	-	1 lb.	Includes 6 feet of clear cord

L I N D S E Y



17195/1



17196/1



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17195/1	(1) 75W Med.	10"	8"	82"	-	3 lbs.	
17196/1	(1) 75W Med.	10"	10"	84"	-	3 lbs.	

C H A P E A U

The Chapeau pendants offer a touch of whimsy with a dignified Matte Black finish. This European inspired design unleashes creative potential amid a variety of settings.



17211/1



17201/1



17221/1



17210/1



17220/1



17200/1



S O R E N S O N

These sweeping curved-shaped pendants present a modern elegance with functional downlight. Finishes include Oil Rubbed Bronze, Gloss Black, and Gloss White.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17200/1	(1) 75W Med.	10"	12"	86"	-	2 lbs.	Oil Rubbed Bronze finish
17201/1	(1) 75W Med.	14"	8"	82"	-	2 lbs.	Oil Rubbed Bronze finish
17210/1	(1) 75W Med.	10"	12"	86"	-	2 lbs.	Gloss Black finish
17211/1	(1) 75W Med.	14"	8"	82"	-	2 lbs.	Gloss Black finish
17220/1	(1) 75W Med.	10"	12"	86"	-	2 lbs.	Gloss White finish
17221/1	(1) 75W Med.	14"	8"	82"	-	2 lbs.	Gloss White finish



31292/5



31291/1



31290/1




31293/5



C O R I S A N D E

The Corisande collection brings together various designer elements to create a stunning free-flowing presentation. Twisted arms radiate from a solid crystal center column which gracefully support clear crystal balls, frosted glass diffusers and silver organza drum shades. The shades are cleverly held by clear glass discs with no visible connecting hardware, giving the appearance that they are free floating. A Polished Nickel finish completes this bold statement.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31290/1	(1) 40W G9 (included)	8"	17"	10"	3 lbs.	Shade included
31291/1	(1) 40W G9 (included)	12"	12"	8"	5 lbs.	Shade included (1) 6" & (3) 12" extension rods w/hang straight included
31292/5	(5) 40W G9 (included)	30"	24"	-	17 lbs.	
31293/5	(5) 40W G9 (included)	30"	24"	-	17 lbs.	Shades included



1470/1



1475/6



1478/2



1477/1



1474/1



1471/2



1476/6+3



1472/3




R E F R A C T I O N

A refraction is defined as a bending of a wave path of light. The Refraction collection captures this fascinating phenomenon with elements that seem to reflect off of a stationary object and bounce into various trajectories. Finished in Polished Chrome.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1470/1	(1) 40W G9 (included)	7"	5"	9"	1 lb.	
1471/2	(2) 40W G9 (included)	16"	7"	8"	3 lbs.	
1472/3	(3) 40W G9 (included)	25"	7"	8"	4 lbs.	
1474/1	(1) 40W G9 (included)	7"	9"	-	2 lbs.	(1) 6" and (2) 12" extension rods with hang straight included
1475/6	(6) 40W G9 (included)	26"	13"	-	7 lbs.	(1) 6" and (2) 12" extension rods with hang straight included
1476/6+3	(9) 40W G9 (included)	31"	16"	-	10 lbs.	(1) 6" and (2) 12" extension rods with hang straight included
1477/1	(1) 40W G9 (included)	7"	4"	-	1 lb.	Includes 6 feet of clear cord
1478/2	(2) 40W G9 (included)	15"	18"	9"	4 lbs.	

Each item number can be paired with any of these available colors' codes, as shown below:



Mars = MAR

Caribbean = CAR

Jasper = JAS

Creme White = CRW

1475/6*



Width: 26"
Height: 13"
Bulb: (6) 40W G9 (included)
Weight: 7 lbs.



1470/1*



Width: 7"
Height: 5"
Ext.: 9"
Bulb: (1) 40W G9 (included)
Weight: 1 lb.



1476/6+3*



Width: 31"
Height: 16"
Bulb: (9) 40W G9 (included)
Weight: 10 lbs.



1478/2*



Width: 15"
Height: 18"
Ext.: 9"
Bulb: (2) 40W G9 (included)
Weight: 4 lbs.

1477/1*



Width: 7"
Height: 4"
Bulb: (1) 40W G9 (included)
Weight: 1 lb.
Includes 6' of clear cord



1471/2*




Width: 16"
Height: 7"
Ext.: 8"
Bulb: (2) 40W G9 (included)
Weight: 3 lbs.



1474/1*



Width: 7"
Height: 9"
Bulb: (1) 40W G9 (included)
Weight: 2 lbs.



1472/3*



Width: 25"
Height: 7"
Ext.: 8"
Bulb: (3) 40W G9 (included)
Weight: 4 lbs.

REFRACTION

* When ordering, please include glass color code after item number. On the 3 light Linear bar, please include the "L" as part of the item number. Otherwise, the 3 light Pan will be sent.



11563/15



11562/10



11561/6




11560/2

T W I L I G H T

Bursting with energy, this collection features striated glass rods radiating from a central core. Its energy is "contained" inside a Polished Chrome sphere to complete the dazzling display.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11560/2	(2) 60W G9 (included)	9"	20"	-	7"	5 lbs.	
11561/6	(6) 60W G9 (included)	17"	9"	-	-	7 lbs.	
11562/10	(10) 60W G9 (included)	22"	22"	67"	-	12 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
11563/15	(15) 60W G9 (included)	32"	32"	77"	-	21 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included



11750/15



11751/19



11752/24



11753/29



STARBURST


This collection has graced New York's Metropolitan Opera since its opening in 1964. It features miniature groupings of highly polished faceted crystal balls and larger metal offshoots which extend from the center orb emulating an exploding celestial body. An abundance of light "reacts" brilliantly with the Polished Chrome finish, captivating your senses while inspiring your imagination. This series can serve as an accent or a centerpiece in a wide range of decors.



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11750/15	(15) 60W Cand.	20"	18"	64"	-	13 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
11751/19	(19) 60W Cand.	26"	17"	62"	-	19 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
11752/24	(24) 60W Cand.	36"	19"	65"	-	22 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
11753/29	(29) 60W Cand.	48"	20"	66"	-	37 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
11754/31	(31) 60W Cand.	72"	36"	82"	-	62 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included



11547/19



11830/6



11545/9



11546/16

STARBURST

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11545/9	(9) 40W G9 (included)	18"	21"	59"	-	14 lbs.	
11546/16	(16) 40W G9 (included)	27"	30"	68"	-	18 lbs.	
11547/19	(19) 40W G9 (included)	36"	40"	78"	-	32 lbs.	
11830/6	(6) 40W G9 (included)	19"	10"	-	-	6 lbs.	



31546/18



31545/12



31547/16



Z E B U L A

A cosmic arrangement of steel wire and crystal form the Zebula collection. Interlaced beads of clear crystal exudes a sparkling radiance throughout the Polished Gold or White finished metalwork.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31545/12	(12) 40W G9 (included)	22"	15"	-	-	9 lbs.	
31546/18	(18) 40W G9 (included)	28"	28"	58"	-	25 lbs.	
31547/16	(16) 40W G9 (included)	24"	24"	54"	-	17 lbs.	



31661/6

31660/3



Shown with light off

11725/LED

11728/LED

11727/LED

LED

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31660/3	(3) 40W G9 (included)	17"	17"	49"	-	8 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
31661/6	(6) 40W G9 (included)	24"	24"	56"	-	10 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11725/LED	16W-1458 Lumen LED (integrated)	16"	9"	-	-	4 lbs.	3000K, 70 CRI, Dimmable
11727/LED	36W-3402 Lumen LED (integrated)	16"	16"	60"	-	6 lbs.	3000K, 70 CRI, Dimmable
11728/LED	72W-6912 Lumen LED (integrated)	23"	23"	66"	-	12 lbs.	3000K, 70 CRI, Dimmable

CRYSTAL ORBS

This series features crystal lined rings that can be rotated to create a series of concentric circles for a myriad of patterns and light contrasts. An Oiled Rubbed Bronze finish defines each ring, distinguishing the metalwork from the clear crystal.

LIGHT SPHERES

This collection features Chrome plated glass balls which appear to "float" inside a laser cut stainless steel frame. Hundreds of LED lights mounted to the inside of the frame reflect the inner elements for added illusion and a captivating performance.



11731/LED



11729/LED



11730/LED

LED

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
11729/LED	29W-2592 Lumen LED (integrated)	13"	18"	58"	-	10 lbs.	3000K, 70 CRI, Dimmable
11730/LED	25W-2400 Lumen LED (integrated)	13"	15"	54"	-	7 lbs.	3000K, 85 CRI
11731/LED	25W-2400 Lumen LED (integrated)	13"	15"	54"	-	7 lbs.	3000K, 85 CRI

CRYSTAL SPHERE

These crystal spheres feature LED lights that emit a brilliant light that dances among the bands of tapered crystals. Available in Polished Chrome or Spanish Bronze finish.



82030/6

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
82030/6	(6) 40W G9 (included)	24"	20"	-	9 lbs.	Polished Chrome finish (1) 6" & (2) 12" extension rods w/ hang straight included

SATURN

Contemporary design of significant celestial proportions. The Saturn fixture is a modern interpretation of the heavenly body featuring intersecting rings of square crystal and a Polished Chrome finish.

30007/42




30006/13




ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
30006/13	(13) 40W G9 (included)	22"	22"	-	16 lbs.	
30007/42	(42) 40W G9 (included)	36"	36"	-	62 lbs.	

O D Y S S E Y

Carefully faceted 32% leaded crystals are set within delicately formed chrome plated metal strips in the Odyssey collection. The merging of these two materials provides a mesmerizing experience for the senses. When illuminated, light reflects amongst the crystal and Polished Chrome finish displaying rich color spectrums and visual motion while inert.

11233/3




Shown as semi flush

ITEM NO.	BULB	W	H	WEIGHT	ADDITIONAL DETAILS
11233/3	(3) 60W Cand.	10"	23"	9 lbs.	Chain hung or semi flush adaptable

C R Y S T O R I A

The Crystoria collection exhibits a new interpretation of the traditional lantern with its geometric crystal beaded motif. Finished in Polished Chrome, this lantern series blends traditional elegance with modern design elements.



19100/4



19102/4



M A R I A N A

This series features fixtures that use mirror as the foremost design element. Each item has a unique silhouette that blends old world elegance with modern allure.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
19100/4	(4) 60W Cand.	25"	25"	68"	-	9 lbs.	Speckled Silver finish
19102/4	(4) 60W Cand.	24"	31"	70"	-	9 lbs.	Speckled Silver finish



19101/4



19103/4



M A R I A N A

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
19101/4	(4) 60W Cand.	25"	30"	70"	-	12 lbs.	Weathered Silver finish
19103/4	(4) 60W Cand.	26"	32"	72"	-	8 lbs.	Blackened Silver finish



LED

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
17165/1	(1) 5W-600 Lumen LED (included)	3"	5"	79"	-	2 lbs.	3200K, 80 CRI
17166/3	(3) 5W-1800 Lumen LED (included)	19"	5"	79"	3"	4 lbs.	3200K, 80 CRI

A L E A

The Polished Chrome plated structure of this mini-pendant presents a generous, precisely cut crystal which crisply diffuses an integrated LED light.



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
83000/3	(3) 60W Cand.	16"	23"	-	18 lbs.	Clear Crystal, Polished Nickel finish
83001/6	(6) 60W Cand.	25"	29"	-	27 lbs.	Clear Crystal, Polished Nickel finish

L I N D I S F A R N E

The Lindisfarne pendant fixture will add dramatic flair to your living space. A Polished Nickel finished sphere encircles ribbed crystal diffusers that refract a crisp, distinctive light.



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31240/2	(2) 60W Cand.	12"	7"	-	6 lbs.	Polished Chrome finish, clear crystal
31241/2	(2) 60W Cand.	12"	6"	-	6 lbs.	Polished Chrome finish, clear crystal
31242/3	(3) 60W Cand.	16"	7"	-	10 lbs.	Polished Chrome finish, clear crystal
31244/4	(4) 60W Cand.	12"	11"	-	16 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included

CRYSTAL FLUSHMOUNTS

These attractive designs are made of high quality crystal in a variety of patterns, shapes, and sizes. Finished in Polished Chrome with clear crystal.



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
46185/3	(3) 40W G9 (included)	13"	11"	-	-	8 lbs.	

CLEARVIEW

This semi flush is fully dressed in cut crystal that refracts light against an elegant Polished Chrome finish.



30015/13



30021/13



30023/5



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
30015/13	(13) 20W G4 (included)	19"	10"	-	18 lbs.	
30021/13	(13) 20W G4 (included)	19"	10"	-	18 lbs.	
30023/5	(5) 20W G4 (included)	13"	10"	-	7 lbs.	



30020/12



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
30020/12	(12) 20W G4 (included)	30"	10"	11"	31 lbs.	

R A D O S

The Rados flush mount goes beyond functional with solid rings of high quality Polished Chrome. Clustered in the center, an abundance of faceted crystal balls hang from slender chrome rods. An additional ring of crystal balls encircle the inside of the frame.

C O R T I N A

The Cortina chandelier creates an architectural crosshatch pattern utilizing horizontal Polished Chrome framework with slender chrome rods arranged vertically for perfect symmetry. Its rectangular shape is especially suitable for kitchens and dining rooms or modern linear spaces.



OPTIX

Vibrant and unique crystal collection with stunning 32% leaded crystal and a Polished Chrome finish.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1990/3	(3) 60W Cand.	12"	7"	-	4 lbs.	
1991/1	(1) 100W Med.	10"	13"	-	5 lbs.	
2595/1	(1) 60W Cand.	5"	11"	6"	2 lbs.	
2993/3	(3) 60W Cand.	23"	12"	13"	5 lbs.	
2997/1A	(1) 60W Cand.	4"	6"	-	2 lbs.	Includes 6 feet of clear cord
11228/1	(1) 60W Cand.	5"	7"	4"	2 lbs.	ADA Compliant
11229/2	(2) 60W Cand.	14"	7"	4"	4 lbs.	
11230/3	(3) 60W Cand.	21"	7"	4"	6 lbs.	



31581/6



31580/3



31591/6



31590/3



Z O E Y

This collection features a double layer of cascading crystal suspended within three glass rings emulating the flow and mist of a formidable waterfall. The Polished Chrome finish is complemented by either clear or amber teak glass and crystal.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31580/3	(3) 60W Cand.	16"	12"	-	-	13 lbs.	
31581/6	(6) 60W Cand.	20"	44-58"	58"	-	44 lbs.	Crystal rows can be removed from bottom for desired height
31590/3	(3) 60W Cand.	16"	12"	-	-	13 lbs.	
31591/6	(6) 60W Cand.	20"	44-58"	58"	-	44 lbs.	Crystal rows can be removed from bottom for desired height



14063/6



14063/6
 Shown Unlit



14060/1



14061/2



14062/3

P A R I S I E N N E

This high fashion collection features Silver Leaf finished metal ovals that surround crystal elements. This metal and crystal assembly cascades harmoniously from the top of the fixture through a translucent chrome shade that reflects light downward for added drama.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
14060/1	(1) 60W Cand.	11"	18"	6"	3 lbs.	Sconce
14061/2	(2) 60W Med.	12"	18"	-	3 lbs.	
14062/3	(3) 60W Med.	22"	47"	-	20 lbs.	
14063/6	(6) 60W Med.	26"	48"	-	44 lbs.	



30008/3



30025/15



30024/9



30026/18



30014/7



M O L E C U L A R

With a fantastic design resembling the structure of a molecule, the Molecular collection exhibits groups of "atoms" made of iridescent blown glass. With a Chrome Plated finish, this collection has a continuous network of tapered metal extensions that seamlessly connect each light in a sculpture-like fashion.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
30008/3	(3) 20W G4 (included)	9"	9"	5"	2 lbs.	Comes with an electronic transformer
30014/7	(7) 20W G4 (included)	11"	17"	9"	5 lbs.	Comes with an electronic transformer
30024/9	(9) 20W G4 (included)	13"	18"	-	10 lbs.	Comes with an electronic transformer
30025/15	(15) 10W G4 (included)	25"	19"	-	20 lbs.	Comes with an electronic transformer
30026/18	(18) 10W G4 (included)	26"	16"	-	18 lbs.	Comes with an electronic transformer



Shown as semi-flush


16011/1

16012/3

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
16011/1	(1) 60W Med.	12"	10"	-	4 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
16012/3	(3) 60W Med.	21"	9"	-	10 lbs.	(1) 4", (1) 6" & (3) 12" extension rods w/hang straight included

WINTER FOREST

True art and workmanship is realized in the Winter Forest collection, which shapes nature into a sleek form. Finished in Aged Silver, this series has an organic metal overlay of lovely branches and crystal accents with an organza diffuser that softens the light.



30031/3

30032/10

30033/10


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
30031/3	(3) 20W G4 (included)	16"	16"	9"	2 lbs.	
30032/10	(10) 20W G4 (included)	40"	39"	20"	5 lbs.	
30033/10	(10) 20W G4 (included)	24"	37"	16"	6 lbs.	

VIVIANA

The Viviana collection is a modern interpretation of nature with branches of Polished Chrome and clear glass "buds" at their tips. Each fixture is lit by low voltage halogen bulbs nested inside of clear crystal florets.



53001/3



Shown as semi-flush



53000/1



53002/1



10303/3



10313/3



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
53000/1	(1) 60W Med.	7"	8"	82"	-	1 lb.	
53001/3	(3) 60W Med.	18"	8"	82"	-	3 lbs.	
53002/1	(1) 60W Cand.	9"	8"	-	5"	1 lb.	Pocket Sconce

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10303/3	(3) 60W Med.	18"	9"	-	12 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
10313/3	(3) 60W Med.	18"	9"	-	12 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included

AUTUMN BREEZE

This series captures the essence of nature with warm, earth-tone colors and a fresh design concept finished in Brushed Nickel. An abstract pattern, reminiscent of blowing leaves in the wind, is placed on clear material to give a light, airy feel while an inner beige fabric drum provides the backdrop for depth and a soft diffusion of light.

CRYSTALS

This series showcases an organza outer shade with a "floating" white fabric inner shade, providing a sleek three-dimensional effect. A clear glass diffuser holding hundreds of clear crystals provides contrast to the smooth drum shades and transforms down light into a shimmering work of art. Choose from a Polished Chrome finish with silver organza shade or Black Chrome with a black organza shade.



Shown in an extended configuration

F A B R I C C Y L I N D E R S

These large drum pendants offer unique design possibilities with various suspension configurations. Each textured beige fabric drum shade has a complete socket hardware assembly inside for added value and durability. Hardware finished in Satin Nickel with clear cord.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
20160/4	(4) 100W Med.	12"	36"		4 lbs.	Includes 6 feet of clear cord
20160/12L	(12) 100W Med.	43"	36"	12"	15 lbs.	Includes 6 feet of clear cord
20160/12R	(12) 100W Med.	28"	36"		17 lbs.	Includes 6 feet of clear cord
20160/20R	(20) 100W Med.	33"	36"		27 lbs.	Includes 6 feet of clear cord



19061/1



19065/3



19030/2



19031/1



19063/5



19060/2



19033/5



M O D E R N O R G A N I C S

The Modern Organics collection blends the beauty of nature with luxurious design. Displayed within each fixture, sustainable natural materials are embedded within clear panels for unparalleled quality and style. Offered in a wide range of organic materials complimented by uncluttered lines of Polished Chrome hardware.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
19030/2	(2) 60W Med.	7"	11"	4"	3 lbs.	White Sawgrass, ADA Compliant
19031/1	(1) 60W Med.	6"	7"	-	2 lbs.	White Sawgrass, Includes 6 feet of clear cord
19033/5	(5) 60W Med.	24"	7"	-	16 lbs.	White Sawgrass, Includes 6 feet of cable
19060/2	(2) 60W Med.	7"	11"	4"	3 lbs.	Bamboo Stems, ADA Compliant
19061/1	(1) 60W Med.	6"	7"	-	2 lbs.	Bamboo Stems, Includes 6 feet of clear cord
19063/5	(5) 60W Med.	24"	7"	-	16 lbs.	Bamboo Stems, Includes 6 feet of cable
19065/3	(3) 60W Med.	14"	9"	-	7 lbs.	Bamboo Stems



31625/4




31635/4



ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31625/4	(4) 60W Cand.	15"	6"	-	-	8 lbs.	
31635/4	(4) 60W Cand.	15"	6"	-	-	8 lbs.	



31035/2



31038/3



31037/1



31039/5



31036/1



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31035/2	(2) 60W Cand.	11"	8"	5"	2 lbs.	Pocket Sconce
31036/1	(1) 60W Med.	8"	20"	-	4 lbs.	
31037/1	(1) 60W Med.	8"	13"	-	2 lbs.	Includes 6 feet of clear cord
31038/3	(3) 60W Med.	16"	8"	-	2 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31039/5	(5) 60W Med.	24"	8"	-	5 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included

R E G I S

Amber teak crystal encircles the outside and inside layers of the beige fabric drum shade.

S K Y L I N E


A city skyline is carefully etched into stainless steel. When illuminated, the energy of a bustling city awakens with buildings and skyscrapers taking on a three dimensional appearance. The series is finished in a skillfully Polished Stainless Steel with a sparkling white diffuser.



10125/5



10172/1



10173/3

Shown as semi-flush



10174/5

ITEM NO.	BULB	W	H	WEIGHT	ADDITIONAL DETAILS
10125/5	(5) 60W Med.	23"	7"	20 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10172/1	(1) 60W Med.	8"	8"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
10173/3	(3) 60W Med.	18"	8"	-	8 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
10174/5	(5) 60W Med.	23"	8"	-	12 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included

Z A R A H

The Zarah pendant offers modern design elements coupled with high quality craftsmanship. A fabric drum shade provides the backdrop for a Polished Nickel finished frame and laser cut ovals literally link together like a chain, this pendant combines cutting edge style and jewelry-like appeal. A frosted white glass diffuser emits a soft yet functional light.

A N A S T A S I A

Captivating arrays of ovals etched out of a single sheet of steel are silhouetted by a light silver fabric diffuser on the inside of this drum shaped series. Completed with an impeccable Polished Nickel finish.



31042/3



31041/1



31046/3



31045/1



31040/2



31043/5



31048/1



31044/2



31047/5



MEDINA

Etched curved corner rectangles are brilliantly enhanced by the diffused light within this drum shaped fixture. The appearance is further defined by the Polished Stainless Steel finish with a sparkling white diffuser or an Aged Bronze finish with an amber diffuser.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31040/2	(2) 60W Cand.	11"	8"	5"	2 lbs.	Pocket sconce
31041/1	(1) 60W Med.	8"	13"	-	2 lbs.	Includes 6 feet of cord
31042/3	(3) 60W Med.	16"	8"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31043/5	(5) 60W Med.	24"	8"	-	5 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31044/2	(2) 60W Cand.	11"	8"	5"	2 lbs.	Pocket sconce
31045/1	(1) 60W Med.	8"	13"	-	2 lbs.	Includes 6 feet of cord
31046/3	(3) 60W Med.	16"	8"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31047/5	(5) 60W Med.	24"	8"	-	5 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31048/1	(1) 100W Med.	10"	15"	11-24"	3 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box.




WOODLAND SUNRISE

Etched into stainless steel, a serene tree-lined meadow is revealed with intricate branch detailing. An Aged Bronze finish with an amber diffuser maximizes the realism of the setting.

ITEM NO.	BULB	W	H	MAX. H	EXT.	WEIGHT	ADDITIONAL DETAILS
31069/1	(1) 100W Med.	10"	15"	-	11-24"	3 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box.
31070/2	(2) 60W Cand.	11"	8"	-	5"	2 lbs.	Pocket Sconce
31072/1	(1) 60W Med.	8"	20"	-	-	4 lbs.	
31073/1	(1) 60W Med.	8"	13"	-	-	2 lbs.	Includes 6 feet of cord
31074/3	(3) 60W Med.	16"	8"	-	-	4 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31075/5	(5) 60W Med.	24"	8"	-	-	5 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included



31105/4



Shown as semi-flush



31101/3



31106/6




31100/2



31102/1



Shown as semi-flush



31103/1




31104/4



GENEVIEVE

This series offers a brilliant display of shimmering crystal with upscale aesthetics. High quality polished crystal is laced into a lattice patterned Polished Chrome metal band, creating a stunning interplay of light and texture. The design is further enriched by a frosted glass diffuser and crystal finial.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31100/2	(2) 60W Cand.	10"	6"	4"	2 lbs.	Pocket Sconce, ADA Compliant
31101/3	(3) 100W Med.	16"	10"	-	8 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31102/1	(1) 100W Med.	10"	6"	-	4 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31103/1	(1) 100W Med.	8"	9"	-	5 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31104/4	(4) 100W Med.	31"	6"	11"	17 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31105/4	(4) 100W Med.	21"	8"	-	13 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31106/6	(6) 100W Med.	29"	11"	-	26 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included



RETROVIA

During the 1950s, there was a renewed sense of style and design from consumer products to fashion and beyond. This design movement coined the term “mid-century modern” which became a leading design movement. Finished in Polished Nickel, this collection embodies the excitement of the time period with laser cut circles, opal etched cylindrical glass, and a white diffuser that accents the drum and vanity fixtures.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31020/2	(2) 60W Cand.	12"	6"	5"	4 lbs.	Pocket Sconce
31021/1	(1) 60W Med.	10"	5"	4"	2 lbs.	Pocket Sconce, ADA Compliant
31022/2	(2) 60W Med.	17"	5"	4"	4 lbs.	ADA Compliant
31023/4	(4) 60W Med.	28"	5"	4"	8 lbs.	ADA Compliant
31024/3	(3) 60W Med.	16"	7"	-	5 lbs.	Flush mount
31025/3	(3) 60W Med.	20"	6"	-	8 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31026/5	(5) 60W Cand.	24"	24"	-	11 lbs.	



CEILING



11463/3



11453/3




66111-2



66411-2



66441-2



11826/4




66121-2



66131-2



66141-2



11825/3



66419/3



66418/2



66631-2



66421-2




66431-2



31422/3



31421/2




46122/2




ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11453/3	(3) 60W Cand.	15"	5"	-	8 lbs.	Oiled Bronze finish, clear ribbed glass
11463/3	(3) 60W Cand.	15"	5"	-	8 lbs.	Brushed Nickel finish, clear ribbed glass
66111-2	(2) 60W Med.	13"	5"	-	6 lbs.	Polished Nickel with White Glass
66121-2	(2) 60W Med.	13"	5"	-	6 lbs.	Satin Nickel with White Glass
66131-2	(2) 60W Med.	13"	5"	-	6 lbs.	Oiled Bronze with Amber Glass
66141-2	(2) 60W Med.	13"	5"	-	6 lbs.	Antique Copper with White Glass
66421-2	(2) 60W Med.	13"	5"	-	6 lbs.	Satin Nickel with Cappa Shells
66431-2	(2) 60W Med.	13"	5"	-	6 lbs.	Oiled Bronze with Cappa Shells
66631-2	(2) 60W Med.	13"	5"	-	6 lbs.	Oiled Bronze finish with White Glass


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11825/3	(3) 60W Med.	16"	9"	-	5 lbs.	Oil Rubbed Bronze finish
11826/4	(4) 60W Med.	24"	13"	-	11 lbs.	Oil Rubbed Bronze finish
31421/2	(2) 60W Med.	12"	5"	-	4 lbs.	Brushed Nickel finish, diamond tread aluminum
31422/3	(3) 60W Med.	16"	5"	-	6 lbs.	Brushed Nickel finish, diamond tread aluminum
46122/2	(2) 60W Med.	12"	5"	-	10 lbs.	Aged Brass finish
66411-2	(2) 60W Med.	13"	5"	-	6 lbs.	Polished Nickel with Cappa Shells
66418/2	(2) 60W Med.	13"	5"	-	7 lbs.	Oil Rubbed Bronze finish
66419/3	(3) 60W Med.	17"	5"	-	10 lbs.	Oil Rubbed Bronze finish
66441-2	(2) 60W Med.	13"	5"	-	6 lbs.	Antique Copper with Cappa Shells



46123/3




46120/2




46121/3



46130/2




46131/3



46112/2



46102/2




46103/3




46100/2



46113/3



46110/2



46111/3




46101/3




46132/2



46133/3



63021-2



31211/2



11465/3



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
46100/2	(2) 60W Med.	12"	5"	-	9 lbs.	Polished Nickel finish
46101/3	(3) 60W Med.	16"	5"	-	14 lbs.	Polished Nickel finish
46102/2	(2) 60W Med.	12"	5"	-	10 lbs.	Polished Nickel finish
46103/3	(3) 60W Med.	16"	5"	-	15 lbs.	Polished Nickel finish
46120/2	(2) 60W Med.	12"	5"	-	9 lbs.	Aged Brass finish
46121/3	(3) 60W Med.	16"	5"	-	14 lbs.	Aged Brass finish
46123/3	(3) 60W Med.	16"	5"	-	15 lbs.	Aged Brass finish
46132/2	(2) 60W Med.	12"	5"	-	10 lbs.	Oil Rubbed Bronze finish
46133/3	(3) 60W Med.	16"	5"	-	15 lbs.	Oil Rubbed Bronze finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11465/3	(3) 60W Med.	15"	5"	-	7 lbs.	Brushed Nickel finish, opal white glass
31211/2	(2) 60W Med.	12"	5"	-	7 lbs.	Polished Nickel finish, Bulb #1092 optional
46110/2	(2) 60W Med.	12"	5"	-	9 lbs.	Brushed Nickel finish
46111/3	(3) 60W Med.	16"	5"	-	14 lbs.	Brushed Nickel finish
46112/2	(2) 60W Med.	12"	5"	-	10 lbs.	Brushed Nickel finish
46113/3	(3) 60W Med.	16"	5"	-	15 lbs.	Brushed Nickel finish
46130/2	(2) 60W Med.	12"	5"	-	9 lbs.	Oil Rubbed Bronze finish
46131/3	(3) 60W Med.	16"	5"	-	14 lbs.	Oil Rubbed Bronze finish
63021-2	(2) 60W Med.	12"	5"	-	7 lbs.	Oiled Bronze finish, Bulb #1092 optional



17250/2




17230/2



17240/2



11451/2



11464/2



66254-2



15015/2



15025/2



11445/3




46044/4




20101/3



20100/2



11440/2



11441/2



11450/2



20131/3



11226/2



11227/3



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11440/2	(2) 60W Med.	13"	5"	-	4 lbs.	Brushed Nickel finish, opal white glass
11441/2	(2) 60W Med.	16"	5"	-	7 lbs.	Brushed Nickel finish, opal white glass
11445/3	(3) 60W Med.	17"	6"	-	9 lbs.	Polished Chrome finish, frosted glass
11450/2	(2) 60W Med.	13"	5"	-	4 lbs.	Oiled Bronze finish, opal white glass
15015/2	(2) 60W Med.	13"	6"	-	7 lbs.	Polished Chrome finish
15025/2	(2) 60W Med.	13"	6"	-	7 lbs.	Oiled Bronze finish
17230/2	(2) 60W Med.	13"	5"	-	5 lbs.	Polished Chrome finish
17240/2	(2) 60W Med.	13"	5"	-	5 lbs.	Brushed Nickel finish
17250/2	(2) 60W Med.	13"	5"	-	5 lbs.	Oil Rubbed Bronze finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11226/2	(2) 60W Med.	13"	6"	-	7 lbs.	Polished Chrome finish
11227/3	(3) 60W Med.	16"	7"	-	9 lbs.	Polished Chrome finish
11451/2	(2) 60W Med.	16"	5"	-	7 lbs.	Oiled Bronze finish, opal white glass
11464/2	(2) 60W Med.	13"	6"	-	8 lbs.	Brushed Nickel finish, opal white glass
20100/2	(2) 60W Med.	13"	6"	-	4 lbs.	Deep Rust finish
20101/3	(3) 60W Med.	16"	6"	-	7 lbs.	Deep Rust finish
20131/3	(3) 60W Med.	16"	6"	-	7 lbs.	Polished Chrome finish
46044/4	(4) 60W Cand.	16"	11"	-	10 lbs.	Mocha finish, curved crystal
66254-2	(2) 60W Med.	13"	5"	-	6 lbs.	Oiled Bronze with White glass



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1511/2	(2) 60W Med.	13"	6"	-	5 lbs.	Antique Silver finish
1513/2	(2) 60W Med.	15"	5"	-	8 lbs.	Antique Silver finish
1515/2	(2) 60W Med.	16"	7"	-	8 lbs.	Antique Silver finish
5962/3	(3) 60W Cand.	13"	7"	-	6 lbs.	Dark Bronze finish
5963/6	(6) 60W Cand.	17"	10"	-	10 lbs.	Dark Bronze finish
6232/4	(4) 60W Cand.	16"	11"	-	11 lbs.	Sunset Silver finish
11225/2	(2) 60W Med.	13"	8"	-	7 lbs.	Polished Chrome finish
11480/3	(3) 60W Cand.	12"	8"	-	6 lbs.	Sunset Silver finish, clear crystal
11481/4	(4) 60W Cand.	15"	9"	-	8 lbs.	Sunset Silver finish, clear crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2156/2	(2) 60W Med.	16"	10"	-	9 lbs.	Burnt Bronze finish
2424/2	(2) 60W Med.	18"	12"	-	13 lbs.	Antique Gold finish
2493/4	(4) 60W Cand.	15"	10"	-	11 lbs.	Burnt Bronze finish
6242/4	(4) 60W Cand.	16"	11"	-	11 lbs.	Dark Bronze finish
9319/2	(2) 60W Med.	16"	9"	-	5 lbs.	Mocha finish
11693/2	(2) 60W Cand.	13"	6"	-	6 lbs.	Aged Silver finish, filigree crystal
11694/4	(4) 60W Cand.	17"	6"	-	10 lbs.	Aged Silver finish, filigree crystal
11695/8	(8) 60W Cand.	24"	9"	-	21 lbs.	Aged Silver finish, filigree crystal
16245/6	(6) 60W Cand.	24"	12"	-	23 lbs.	Sunset Silver finish



990-D



990-J



70014-3



22016/2



22040/2



57025/2



70027-2



70007-2



31108/3




8889/2




31551/3



11561/6




31109/3



22011/3



22005/2



11830/6



31545/12



11725/LED
LED

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
990-D	(2) 60W Med.	12"	5"	-	7 lbs.	Fan Kit/Ceiling Mount, White Tiffany Glass
990-J	(2) 60W Med.	14"	5"	-	8 lbs.	Fan Kit/Ceiling Mount, Tiffany glass
22005/2	(2) 60W Cand.	14"	6"	-	4 lbs.	Solid Brass finish
22011/3	(3) 60W Cand.	21"	6"	-	8 lbs.	Brushed Brass finish
31108/3	(3) 60W Cand.	13"	9"	-	5 lbs.	Aged Silver finish
31109/3	(3) 60W Cand.	13"	9"	-	4 lbs.	Oil Rubbed Bronze finish
70007-2	(2) 60W Med.	14"	5"	-	7 lbs.	Matte Black with Cream art glass
70014-3	(3) 60W Med.	16"	6"	-	7 lbs.	Oiled Bronze with Cream glass
70027-2	(2) 60W Med.	13"	4"	-	5 lbs.	Oiled Bronze with Tea Stained glass

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
8889/2	(2) 60W Med.	12"	6"	-	5 lbs.	White Stone finish
11561/6	(6) 60W G9 (included)	17"	9"	-	7 lbs.	Polished Chrome finish
22016/2	(2) 60W Med.	17"	7"	-	6 lbs.	Brushed Brass finish
22040/2	(2) 60W Med.	12"	5"	-	6 lbs.	Brushed Brass finish
31551/3	(3) 60W Med.	19"	8"	-	8 lbs.	Polished Nickel finish, chestnut finish wood
57025/2	(2) 60W Med.	13"	6"	-	5 lbs.	Oil Rubbed Bronze finish
11725/LED	16W-1458 Lumen LED (integrated)	16"	9"	-	4 lbs.	3000K, 70 CRI, Dimmable
11830/6	(6) 40W G9 (included)	19"	10"	-	6 lbs.	Polished Chrome finish
31545/12	(12) 40W G9 (included)	22"	15"	-	9 lbs.	White finish

LED Option LED option available. When ordering include -LED after item number.



31240/2



31241/2




31242/3



31625/4



31635/4



5088/3



30021/13



30023/5



1990/3



11821/3



11820/2



31580/3



31590/3



31024/3



11811/3



11810/2



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1990/3	(3) 60W Cand.	12"	7"	-	4 lbs.	Polished Chrome finish
30021/13	(13) 40W G9 (included)	19"	10"	-	18 lbs.	Polished Chrome finish
30023/5	(5) 20W G4 (included)	13"	10"	-	7 lbs.	Polished Chrome finish
31024/3	(3) 60W Med.	16"	7"	-	5 lbs.	Polished Nickel finish
31240/2	(2) 60W Cand.	12"	7"	-	6 lbs.	Polished Chrome finish, clear crystal
31241/2	(2) 60W Cand.	12"	6"	-	6 lbs.	Polished Chrome finish, clear crystal
31242/3	(3) 60W Cand.	16"	7"	-	10 lbs.	Polished Chrome finish, clear crystal
31580/3	(3) 60W Cand.	16"	12"	-	13 lbs.	Polished Chrome finish, clear crystal
31590/3	(3) 60W Cand.	16"	12"	-	13 lbs.	Polished Chrome finish, amber teal crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
5088/3	(3) 60W Med.	16"	5"	-	5 lbs.	Satin White glass
11810/2	(2) 60W Med.	10"	5"	-	3 lbs.	Oil Rubbed Bronze finish
11811/3	(3) 60W Med.	14"	5"	-	5 lbs.	Oil Rubbed Bronze finish
11820/2	(2) 60W Med.	10"	5"	-	3 lbs.	Brushed Nickel finish
11821/3	(3) 60W Med.	14"	5"	-	5 lbs.	Brushed Nickel finish
31625/4	(4) 60W Cand.	15"	6"	-	8 lbs.	Polished Chrome finish, beige shade, crystal
31635/4	(4) 60W Cand.	15"	6"	-	8 lbs.	Polished Chrome finish, beige shade, amber teal crystal



81041/4



81040/3



81081/4



81080/3



31481/2



57011/LED



LED



57010/LED



LED



57021/LED



LED



57020/LED



LED



57001/LED



LED



57000/LED



LED

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31481/2	(2) 60W Med.	13"	5"	-	4 lbs.	Aged Brass finish, Bulb #1092 optional
81040/3	(3) 60W Cand.	12"	6"	-	7 lbs.	Polished Chrome finish
81041/4	(4) 60W Cand.	16"	6"	-	10 lbs.	Polished Chrome finish
81080/3	(3) 60W Cand.	12"	5"	-	5 lbs.	Polished Chrome finish
81081/4	(4) 60W Cand.	16"	5"	-	7 lbs.	Polished Chrome finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
57000/LED	23W-1460 Lumen LED (integrated)	14"	3"	-	3 lbs.	Brushed Nickel finish, 3000K, 83 CRI, Dimmable
57001/LED	31W-1910 Lumen LED (integrated)	17"	3"	-	5 lbs.	Brushed Nickel finish, 3000K, 83 CRI, Dimmable
57010/LED	23W-1460 Lumen LED (integrated)	14"	3"	-	3 lbs.	Polished Chrome finish, 3000K, 83 CRI, Dimmable
57011/LED	31W-1910 Lumen LED (integrated)	17"	3"	-	5 lbs.	Polished Chrome finish, 3000K, 83 CRI, Dimmable
57020/LED	23W-1460 Lumen LED (integrated)	14"	3"	-	3 lbs.	Oil Rubbed Bronze finish, 3000K, 83 CRI, Dimmable
57021/LED	31W-1910 Lumen LED (integrated)	17"	3"	-	5 lbs.	Oil Rubbed Bronze finish, 3000K, 83 CRI, Dimmable



31237/6 Shown as semi-flush 9" H



11654/2



63011-2



69045/1



69055/1



66191-3



63052-2



31506/4



31424/3



08103-AGB



08101-AGB



08100-AGB



66221-1



69044/1



69054/1



08099-AGB



08097-AGB



08096-AGB

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11654/2	(2) 60W Med.	13"	11"	-	4 lbs.	Oil Rubbed Bronze finish
31237/6*	(6) 60W Med.	22"	4"	-	7 lbs.	Bulb # 1092 optional, Silvered Graphite finish
31424/3**	(3) 60W Med.	16"	9"	-	9 lbs.	Brushed Nickel finish, diamond tread aluminum
31506/4	(4) 60W Cand.	12"	11"	-	8 lbs.	Oil Rubbed Bronze finish
63011-2	(2) 60W Med.	15"	14"	-	8 lbs.	Aged Bronze with White glass
63052-2	(2) 60W Med.	15"	14"	-	8 lbs.	Silvered Graphite finish
66221-1	(1) 75W Med.	11"	11"	-	3 lbs.	Oiled Bronze with White glass
69044/1	(1) 60W Med.	9"	10"	-	3 lbs.	Satin Nickel finish
69054/1	(1) 60W Med.	9"	10"	-	3 lbs.	Oil Rubbed Bronze finish

* (1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
 ** (1) 6" and (3) 12" extension rods with hang straight included

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08096-AGB	(3) 75W Med.	16"	12"	-	5 lbs.	Antique Golden Bronze with Amber Antique glass
08097-AGB*	(3) 75W Med.	10"	9"	-	4 lbs.	Antique Golden Bronze with Amber Antique glass
08099-AGB	(3) 75W Med.	19"	14"	-	7 lbs.	Antique Golden Bronze with Amber Antique glass
08100-AGB*	(3) 75W Med.	12"	13"	-	3 lbs.	Antique Golden Bronze with Amber Antique glass
08101-AGB	(3) 75W Med.	16"	11"	-	5 lbs.	Antique Golden Bronze with Amber Antique glass
08103-AGB*	(3) 75W Med.	10"	10"	-	3 lbs.	Antique Golden Bronze with Amber Antique glass
66191-3	(3) 75W Med.	14"	10"	-	5 lbs.	Oiled Bronze with Restoration glass
69045/1	(1) 60W Med.	12"	12"	-	4 lbs.	Satin Nickel finish
69055/1	(1) 60W Med.	12"	12"	-	4 lbs.	Oil Rubbed Bronze finish

* Regular medium base torpedo bulb recommended



08092-AGB



08093-AGB



08094-AGB



66234-1



14259/5



14131/4



08095-AGB




66335-3



08098-AGB



31433/8



31432/6



31431/3



66092-3




66093-4




17053/1



31773/3
 Shown as semi-flush 13" H



31774/5
 Shown as semi-flush 14" H



31771/6
 Shown as semi-flush 16" H

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08092-AGB*	(3) 75W Med.	12"	12"	-	3 lbs.	Antique Golden Bronze with Amber glass
08093-AGB	(4) 75W Med.	20"	13"	-	8 lbs.	Antique Golden Bronze with Amber glass
08094-AGB	(3) 75W Med.	15"	15"	-	6 lbs.	Antique Golden Bronze with Amber glass
08095-AGB	(4) 75W Med.	19"	14"	-	8 lbs.	Antique Golden Bronze with Amber glass
08098-AGB*	(3) 75W Med.	11"	10"	-	3 lbs.	Antique Golden Bronze with Frosted glass and clear highlights
17053/1	(1) 60W Med.	8"	9"	-	3 lbs.	Polished Chrome finish
66092-3*	(3) 75W Med.	12"	12"	-	3 lbs.	Dark Silver with White Antique glass
66093-4	(4) 75W Med.	20"	13"	-	10 lbs.	Dark Silver with White Antique glass
66335-3	(3) 75W Med.	12"	9"	-	3 lbs.	Oiled Bronze with Frosted glass and clear highlights

* Regular medium base torpedo bulb recommended

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
14131/4	(4) 60W Cand.	17"	16"	-	6 lbs.	Vintage Rust finish
14259/5	(5) 60W Med.	20"	16"	-	6 lbs.	Bulb #1092 optional, Wrought Iron Black finish
31431/3	(3) 60W Cand.	23"	11"	-	9 lbs.	Aged Silver finish, crystal
31432/6	(6) 60W Cand.	26"	27"	-	20 lbs.	Aged Silver finish, crystal
31433/8	(8) 60W Cand.	37"	31"	-	29 lbs.	Aged Silver finish, crystal
31771/6*	(6) 60W Cand.	18"	11"	-	13 lbs.	Aged Silver finish, crystal
31773/3	(3) 60W Cand.	12"	22"	-	8 lbs.	Aged Silver finish, crystal
31774/5**	(5) 60W Cand.	20"	9"	-	13 lbs.	Aged Silver finish, crystal
66234-1	(1) 75W Med.	11"	11"	-	3 lbs.	Polished Nickel with White glass

* (1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

** (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
5964/3	(3) 60W Cand.	13"	14"	-	8 lbs.	Dark Bronze finish
11286/4	(4) 60W Cand.	13"	10"	-	7 lbs.	Antique Bronze finish
11710/6	(6) 60W Cand.	13"	20"	-	10 lbs.	Aged Silver finish
11711/8	(8) 60W Cand.	17"	23"	-	13 lbs.	Aged Silver finish
11720/6	(6) 60W Cand.	13"	20"	-	10 lbs.	Spanish Bronze finish
11721/8	(8) 60W Cand.	17"	23"	-	13 lbs.	Spanish Bronze finish
11781/4	(4) 60W Cand.	16"	14"	-	7 lbs.	Antique Bronze finish, crystal
11782/5	(5) 60W Cand.	21"	17"	-	10 lbs.	Antique Bronze finish, crystal
46045/6	(6) 60W Cand.	22"	23"	-	17 lbs.	Mocha finish, curved crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2402/6	(6) 60W Cand.	20"	14"	-	12 lbs.	Spanish Bronze finish
6233/6	(6) 60W Cand.	20"	21"	-	19 lbs.	Sunset Silver finish
10271/3	(3) 60W Med.	16"	8"	-	9 lbs.	Satin Nickel finish
10281/3	(3) 60W Med.	16"	8"	-	9 lbs.	Aged Bronze finish
11365/1	(1) 60W Med.	19"	11"	-	10 lbs.	Sunset Silver finish
12024/5	(5) 60W Cand.	20"	26"	-	18 lbs.	Mocha finish
12025/6	(6) 60W Cand.	26"	30"	-	26 lbs.	Mocha finish
16243/4*	(4) 60W Cand.	15"	6"	-	11 lbs.	Sunset Silver finish
31007/3	(3) 60W Med.	16"	7"	-	10 lbs.	Renaissance Silver Leaf finish

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included




2157/3



2494/6




2425/3



11773/8



Shown as semi-flush 13" H



11772/6



18096/3



3825/3




2181/3




7956/5



7044/3



7047/6



7046/3




8069/2



8059/2



18111/2



9105/4



20089/3



4052/3



www.elklighting.com

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2157/3	(3) 60W Med.	19"	20"	-	16 lbs.	Burnt Bronze finish
2181/3	(3) 60W Med.	19"	15"	-	12 lbs.	Burnt Bronze finish
2425/3	(3) 60W Med.	21"	19"	-	15 lbs.	Polished Nickel finish
2494/6	(6) 60W Cand.	18"	21"	-	18 lbs.	Antique Bronze finish
3825/3	(3) 60W Cand.	17"	14"	-	4 lbs.	Aged Silver finish
7956/5	(5) 40W G9 (included)	27"	7"	13"	8 lbs.	Aged Bronze finish
8059/2	(2) 60W Med.	24"	12"	-	8 lbs.	Deep Rust finish
8069/2	(2) 60W Med.	24"	12"	-	8 lbs.	Russet Beige finish
18111/2	(2) 60W Med.	17"	14"	-	7 lbs.	Antique White finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
4052/3	(3) 60W Cand.	19"	10"	-	4 lbs.	Antique White finish
7044/3	(3) 60W Cand.	19"	13"	-	8 lbs.	Deep Rust finish
7046/3	(3) 60W Cand.	27"	12"	-	7 lbs.	Deep Rust finish
7047/6	(6) 60W Cand.	38"	13"	-	17 lbs.	Deep Rust finish
9105/4	(4) 40W G9 (included)	36"	10"	-	19 lbs.	Bronze Rust finish
11772/6	(6) 60W Cand.	24"	8"	-	6 lbs.	Burnt Bronze finish
11773/8	(8) 60W Cand.	30"	30"	-	15 lbs.	Burnt Bronze finish
18096/3	(3) 60W Cand.	17"	8"	-	6 lbs.	Cream finish
20089/3	(3) 60W Med.	16"	15"	-	3 lbs.	Darkwood finish



11360/9



31500/2



31504/3



Shown as semi-flush 16" H



937-CB



936-CB



70114-1



10481/3



10482/4



15081/3



08015-TBH



641-BC



70089-1



70021-1



941-TB



931-VA



621-AB



933-TB



934-CB



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
931-VA	(3) 75W Med.	16"	8"	-	10 lbs.	Vintage Antique with Tiffany glass
941-TB	(3) 75W Med.	16"	8"	-	10 lbs.	Tiffany Bronze with White Tiffany Glass
10481/3	(3) 60W Cand.	16"	8"	-	4 lbs.	Polished Chrome finish, crystal
10482/4	(4) 60W Cand.	16"	11"	-	6 lbs.	Polished Chrome finish, crystal
11360/9	(9) 60W Cand.	25"	20"	-	12 lbs.	Aged Silver finish
15081/3*	(3) 60W Med.	15"	16"	-	7 lbs.	Vintage Rust finish
31500/2	(2) 60W Cand.	15"	11"	-	10 lbs.	Polished Nickel finish, K9 crystal beads
31504/3	(3) 60W Cand.	11"	16"	-	7 lbs.	Polished Nickel finish, K9 crystal beads
70021-1	(1) 75W Med.	8"	11"	-	2 lbs.	Matte Black with Tiffany glass

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08015-TBH	(3) 75W Med.	16"	15"	-	7 lbs.	Tiffany Bronze with Highlights and Tiffany glass
621-AB	(3) 75W Med.	14"	13"	-	12 lbs.	Burnished Copper with Cream Tiffany glass
641-BC	(3) 75W Med.	16"	11"	-	10 lbs.	Burnished Copper with Tiffany glass
933-TB	(3) 75W Med.	16"	8"	-	10 lbs.	Tiffany Bronze finish with Tiffany glass
934-CB	(3) 75W Med.	16"	8"	-	10 lbs.	Classic Bronze with Tiffany Glass
936-CB	(3) 75W Med.	16"	8"	-	10 lbs.	Classic Bronze finish
937-CB	(3) 75W Med.	16"	8"	-	10 lbs.	Classic Bronze finish
70089-1	(1) 75W Med.	8"	11"	-	2 lbs.	Burnished Copper with Tiffany glass
70114-1	(1) 75W Med.	8"	11"	-	2 lbs.	Tiffany Bronze with Highlights and Tiffany glass

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



997-AW-01



997-AW-03



997-AW-04



614-CB



15031/3



70065-2



997-AW-07



997-AW-09



997-AW-10



11700/3



11701/4



20061/2



997-AW-12



997-AW-13



997-AW-17



11055/4



31031/3



66380/3



997-AW-19



997-AW-21



997-AW-28

Adjust chains to suit your needs. 18" of chain per socket included

Aged Walnut Finish
 Size: W: 14" H: 16"

Lamp: (3) 75W Med.
 Weight: 13 lbs.

MIX - N - MATCH SHADES

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
614-CB	(3) 75W Med.	16"	14"	-	11 lbs.	Classic Bronze with Tiffany Glass
11055/4	(4) 60W Med.	20"	14"	-	9 lbs.	Brushed Antique Brass finish
15031/3	(3) 60W Med.	13"	7"	-	4 lbs.	Aged Bronze finish
11700/3*	(3) 60W Med.	13"	12"	-	7 lbs.	Spanish Bronze finish, crystal
11701/4*	(4) 60W Med.	23"	19"	-	13 lbs.	Spanish Bronze finish, crystal
20061/2	(2) 60W Med.	15"	9"	-	9 lbs.	Polished Nickel finish
31031/3	(3) 60W Med.	16"	13"	-	8 lbs.	Brushed Antique Brass finish
66380/3	(3) 60W Med.	15"	11"	-	4 lbs.	Rust finish
70065-2	(2) 60W Med.	14"	9"	-	5 lbs.	Tiffany Bronze finish with Tan Mica

* (1) 2.5", (1) 6" & (2) 12" extension rods w/hang straight included

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



46022/4



46021/3



22012/4



31334/3



31456/3



31466/3



22013/8



22006/3



22007/4



31650/3



31262/3



31519/3



22004/4



Shown as semi-flush 17" H



22002/2



63071/2



31529/3



31361/2



31371/2



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
22002/2	(2) 60W Med.	14"	6"	-	5 lbs.	Brushed Brass finish
22004/4	(4) 60W Med.	18"	17"	-	9 lbs.	Brushed Brass finish
22006/3	(3) 60W Med.	16"	18"	-	8 lbs.	Solid Brass finish
22007/4	(4) 60W Med.	24"	20"	-	15 lbs.	Solid Brass finish
22012/4	(4) 60W Med.	25"	22"	-	11 lbs.	Brushed Brass finish
22013/8	(8) 60W Med.	43"	23"	-	18 lbs.	Brushed Brass finish
46021/3	(3) 60W Cand.	14"	21"	-	3 lbs.	Mocha finish
46022/4	(4) 60W Cand.	19"	28"	-	5 lbs.	Mocha finish
63071/2	(2) 60W Med.	20"	13"	-	6 lbs.	Oil Rubbed Bronze finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31262/3	(3) 60W Med.	16"	14"	-	7 lbs.	Brushed Antique Brass finish
31334/3*	(3) 60W Med.	14"	7"	-	7 lbs.	Polished Nickel finish
31361/2	(2) 60W Med.	14"	9"	-	6 lbs.	Aged Silver finish
31371/2	(2) 60W Med.	14"	9"	-	6 lbs.	Aged Bronze finish
31456/3	(3) 60W Cand.	12"	12"	-	6 lbs.	Polished Nickel finish
31466/3	(3) 60W Cand.	12"	12"	-	6 lbs.	Antique Gold Leaf finish
31519/3	(3) 60W Med.	16"	9"	-	6 lbs.	Aged Silver finish
31529/3	(3) 60W Med.	16"	9"	-	6 lbs.	Oil Rubbed Bronze finish
31650/3	(3) 60W Med.	17"	16"	-	5 lbs.	Polished Nickel finish

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included



31284/2



20152/3



46031/3



31122/3



31523/3



Shown as semi-flush 14" H



10411/3



7633/2



7643/2




1743/2



10418/3



73022-3



73032-3



31451/3



31461/3



20006/5



10139/2WHT



10139/2SLV



10140/2



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1743/2	(2) 60W Med.	16"	15"	-	6 lbs.	Aged Bronze finish
7633/2	(2) 60W Med.	16"	15"	-	6 lbs.	Satin Nickel finish
7643/2	(2) 60W Med.	16"	15"	-	6 lbs.	Aged Bronze finish
20006/5	(5) 60W Med.	23"	12"	-	11 lbs.	Antique Silver finish
20152/3	(3) 60W Med.	18"	12"	-	8 lbs.	Satin Nickel finish
31284/2	(2) 60W Med.	12"	10"	-	3 lbs.	Polished Chrome finish
31451/3	(3) 60W Cand.	11"	8"	-	8 lbs.	Oil Rubbed Bronze finish
31461/3	(3) 60W Cand.	11"	8"	-	8 lbs.	Polished Nickel finish
46031/3	(3) 60W Med.	15"	13"	-	3 lbs.	Silver Leaf finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10139/2SLV	(2) 60W Med.	12"	5"	-	4 lbs.	Silver glass, Satin Nickel and Dark Rust finials included
10139/2WHT	(2) 60W Med.	12"	5"	-	4 lbs.	White glass, Satin Nickel and Dark Rust finials included
10140/2	(2) 75W Med.	12"	5"	-	4 lbs.	Cappa Shells, Satin Nickel finish
10411/3	(3) 60W Med.	16"	8"	-	6 lbs.	Satin Nickel finish, shells
10418/3	(3) 60W Med.	16"	8"	-	11 lbs.	Satin Nickel finish, mosaic glass
31122/3	(3) 60W Med.	16"	13"	-	11 lbs.	Aged Silver finish
31523/3*	(3) 60W Med.	18"	6"	-	10 lbs.	Aged Silver finish
73022-3	(3) 60W Med.	16"	11"	-	6 lbs.	Satin Nickel with Cracked glass
73032-3	(3) 60W Med.	16"	11"	-	6 lbs.	Satin Nickel with Cracked glass


* (1) 6", (1) 12" & (1) 24" extension rods w/hang straight included



66921/8
Shown as semi-flush 22" H




57091/4
Bulb #1101 optional



72071-2




16012/3



53001/3



19065/3



72061-2



17248/1



17258/1



10174/5



10173/3



10129/5



46185/3



1991/1



14061/2



10128/3



10329/5



10328/3

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1991/1	(1) 100W Med.	10"	13"	-	5 lbs.	Polished Chrome finish
14061/2	(2) 60W Med.	12"	18"	-	3 lbs.	Silver Leaf finish
17248/1	(1) 75W Med.	12"	9"	-	3 lbs.	Brushed Nickel finish
17258/1	(1) 75W Med.	12"	9"	-	3 lbs.	Oil Rubbed Bronze finish
46185/3	(3) 40W G9 (included)	13"	11"	-	8 lbs.	Polished Chrome finish, crystal
57091/4	(4) 60W Cand.	21"	8"	-	8 lbs.	Oil Rubbed Bronze finish
66921/8	(8) 60W Cand.	26"	33"	-	10 lbs.	Weathered Bronze finish
72061-2	(2) 60W Med.	13"	11"	-	7 lbs.	Brushed Nickel finish
72071-2	(2) 60W Med.	13"	11"	-	7 lbs.	Brushed Nickel finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10128/3*	(3) 60W Med.	16"	8"	-	11 lbs.	Polished Nickel finish
10129/5*	(5) 60W Med.	24"	8"	-	17 lbs.	Polished Nickel finish
10173/3*	(3) 60W Med.	18"	8"	-	8 lbs.	Polished Nickel finish
10174/5*	(5) 60W Med.	23"	8"	-	12 lbs.	Polished Nickel finish
10328/3*	(3) 60W Med.	16"	8"	-	11 lbs.	Aged Bronze finish
10329/5*	(5) 60W Med.	24"	8"	-	17 lbs.	Aged Bronze finish
16012/3**	(3) 60W Med.	21"	9"	-	10 lbs.	Aged Silver finish
19065/3	(3) 60W Med.	14"	9"	-	7 lbs.	Polished Chrome finish
53001/3	(3) 60W Med.	18"	8"	-	3 lbs.	Beige fabric inner drum

* 1-6" and 2-12" extension rods with hang straight included

** (1) 4", (1) 6" & (3) 12" extension rods w/hang straight included




11761/3




31102/1




31101/3



205-WM




202-CL



200-MN



21008/2



21007/2



21005/2

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
200-MN	(3) 60W Med.	17"	6"	-	6 lbs.	Moonshine, Glows in the dark
202-CL	(3) 60W Med.	17"	6"	-	6 lbs.	Clouds
205-WM	(3) 60W Med.	17"	6"	-	6 lbs.	World Map
11761/3	(3) 60W G9 (included)	13"	13"	-	7 lbs.	Polished Chrome finish
21005/2	(2) 60W Med.	13"	4"	-	4 lbs.	White finish
21007/2	(2) 60W Med.	13"	4"	-	4 lbs.	White finish
21008/2	(2) 60W Med.	13"	4"	-	4 lbs.	White finish
31101/3*	(3) 100W Med.	16"	10"	-	8 lbs.	Polished Chrome finish
31102/1*	(1) 100W Med.	10"	6"	-	4 lbs.	Polished Chrome finish

* (1) 6" and (2) 12" extension rods with hang straight included



10152/1PC-*

 Shown in Fire Red



10152/1PC-*

 Shown in Snow White



10152/1PC-*

 Shown in Espresso



10152/1DR-*

 Shown in Fire Red



10152/1DR-*

 Shown in Snow White



10152/1DR-*

 Shown in Espresso



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10152/1DR-*	(1) 60W Med.	6"	9"	7"	2 lbs.	Dark Rust finish
10152/1PC-*	(1) 60W Med.	6"	9"	7"	2 lbs.	Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* Item numbers shown are for frame. Please include glass color code after item #



BATH AND SPA

Reflections of Your Style



11516/2



11515/1



31181/2




31180/1



11517/3



31182/3



11518/4



31183/4



CORRUGATED GLASS

Polished Chrome finish with thick corrugated clear glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11515/1	(1) 60W G9 (included)	5"	11"	4"	5 lbs.	ADA Compliant
11516/2	(2) 60W G9 (included)	20"	5"	4"	9 lbs.	
11517/3	(3) 60W G9 (included)	29"	5"	4"	13 lbs.	
11518/4	(4) 60W G9 (included)	38"	5"	4"	18 lbs.	

ENCASED CRYSTALS

Polished Chrome finish with encased crystals

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31180/1	(1) 60W Cand.	7"	6"	4"	3 lbs.	ADA Compliant
31181/2	(2) 60W Cand.	14"	5"	5"	5 lbs.	
31182/3	(3) 60W Cand.	24"	5"	5"	8 lbs.	
31183/4	(4) 60W Cand.	36"	5"	5"	12 lbs.	



11621/2



11620/1



11631/2



11630/1




11622/3



11632/3



11623/4



11633/4

CHISELED GLASS

Polished Chrome finish with clear frosted glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11620/1	(1) 60W G9 (included)	5"	5"	4"	3 lbs.	ADA compliant
11621/2	(2) 60W G9 (included)	12"	5"	4"	5 lbs.	
11622/3	(3) 60W G9 (included)	20"	5"	4"	7 lbs.	
11623/4	(4) 60W G9 (included)	27"	5"	4"	9 lbs.	

CHISELED GLASS

Brushed Nickel finish with clear frosted glass


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11630/1	(1) 60W G9 (included)	5"	5"	4"	3 lbs.	ADA compliant
11631/2	(2) 60W G9 (included)	12"	5"	4"	5 lbs.	
11632/3	(3) 60W G9 (included)	20"	5"	4"	7 lbs.	
11633/4	(4) 60W G9 (included)	27"	5"	4"	9 lbs.	



10326/2



10328/3




10327/3




10360/1



10128/3



10126/2



10127/3



B R A X T O N

Aged Bronze finish with ribbed glass rods

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10326/2	(2) 100W Med.	14"	4"	4"	3 lbs.	ADA Compliant
10327/3	(3) 100W Med.	28"	4"	4"	5 lbs.	ADA Compliant
10328/3	(3) 60W Med.	16"	8"	-	11 lbs.	(1) 6" & (2) 12" extension rods with hang straight included


B R A X T O N

Polished Nickel finish with ribbed glass rods

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10126/2	(2) 100W Med.	14"	4"	4"	3 lbs.	ADA Compliant
10127/3	(3) 100W Med.	28"	4"	4"	5 lbs.	ADA Compliant
10128/3	(3) 60W Med.	16"	8"	-	11 lbs.	(1) 6" & (2) 12" extension rods with hang straight included
10360/1	(1) 60W Med.	6"	8"	4"	2 lbs.	ADA Compliant



17181/2



17180/1



11431/2



11430/1



17182/3



17183/4



11432/3



VENTOR

Polished Chrome finish backplate with etched stainless steel shades

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17180/1	(1) 40W G9 (included)	8"	6"	4"	1 lb.	ADA Compliant
17181/2	(2) 40W G9 (included)	16"	5"	4"	2 lbs.	
17182/3	(3) 40W G9 (included)	24"	5"	4"	3 lbs.	
17183/4	(4) 40W G9 (included)	33"	5"	4"	4 lbs.	

WILLOW BEND

Polished Chrome finish with laser cut shade and frosted glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11430/1	(1) 60W Cand.	8"	10"	4"	2 lbs.	ADA compliant
11431/2	(2) 60W Cand.	17"	7"	7"	4 lbs.	
11432/3	(3) 60W Cand.	25"	7"	7"	6 lbs.	



11585/2

11286/4



11586/4

11584/1



11587/6



11693/2

11695/8



11694/4



11690/2



11691/4

AMHERST

Antique Bronze finish with polished crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11286/4	(4) 60W Cand.	13"	10"	-	7 lbs.	
11584/1	(1) 60W Cand.	6"	9"	4"	3 lbs.	ADA Compliant
11585/2	(2) 60W Cand.	14"	5"	5"	5 lbs.	
11586/4	(4) 60W Cand.	24"	5"	5"	8 lbs.	
11587/6	(6) 60W Cand.	34"	5"	5"	11 lbs.	

ANDALUSIA

Aged Silver finish with filigree crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11690/2	(2) 60W Cand.	12"	6"	5"	4 lbs.	
11691/4	(4) 60W Cand.	24"	6"	5"	7 lbs.	
11693/2	(2) 60W Cand.	13"	6"	-	6 lbs.	
11694/4	(4) 60W Cand.	17"	6"	-	10 lbs.	
11695/8	(8) 60W Cand.	24"	9"	-	21 lbs.	



31427/2



31426/1



31437/2



31436/1



31428/3



31438/3



31429/4



31439/4



SANTA MONICA


Aged Silver finish with half round frosted white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31426/1	(1) 60W G9 (included)	6"	9"	4"	2 lbs.	ADA compliant
31427/2	(2) 60W G9 (included)	16"	6"	4"	4 lbs.	
31428/3	(3) 60W G9 (included)	23"	6"	4"	5 lbs.	
31429/4	(4) 60W G9 (included)	30"	6"	4"	6 lbs.	

SANTA MONICA

Weathered Bronze finish with gold highlights and half round frosted amber glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31436/1	(1) 60W G9 (included)	6"	9"	4"	2 lbs.	ADA compliant
31437/2	(2) 60W G9 (included)	16"	6"	4"	4 lbs.	
31438/3	(3) 60W G9 (included)	23"	6"	4"	5 lbs.	
31439/4	(4) 60W G9 (included)	30"	6"	4"	6 lbs.	



31415/1



31416/3



11280/1



11281/2



11282/3



11283/4

TALMAGE

Polished Chrome finish with diamond patterned frosted glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31415/1	(1) 60W G9 (included)	7"	5"	5"	2 lbs.	
31416/3	(3) 60W G9 (included)	21"	5"	6"	6 lbs.	

BRISTON


Satin Nickel finish with curved frosted glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11280/1	(1) 40W G9 (included)	7"	8"	4"	2 lbs.	ADA Compliant
11281/2	(2) 40W G9 (included)	19"	6"	5"	4 lbs.	
11282/3	(3) 40W G9 (included)	27"	6"	5"	5 lbs.	
11283/4	(4) 40W G9 (included)	36"	6"	5"	7 lbs.	


*Satin Nickel finish coordinates with Brushed Nickel finish.



31024/3




31020/2



11596/2



11761/3



31022/2




31021/1



11597/3



11595/1



31023/4



11598/4

RETROVIA

Polished Nickel finish with opal etched glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31020/2	(2) 60W Cand.	12"	6"	5"	4 lbs.	
31021/1	(1) 60W Med.	10"	5"	4"	2 lbs.	ADA Compliant
31022/2	(2) 60W Med.	17"	5"	4"	4 lbs.	ADA Compliant
31023/4	(4) 60W Med.	28"	5"	4"	8 lbs.	ADA Compliant
31024/3	(3) 60W Med.	16"	7"	-	5 lbs.	


SCULPTIVE

Matte Nickel and Polished Nickel finish with scalloped frosted glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11595/1	(1) 60W G9 (included)	5"	7"	6"	2 lbs.	
11596/2	(2) 60W G9 (included)	15"	5"	6"	4 lbs.	
11597/3	(3) 60W G9 (included)	22"	5"	6"	6 lbs.	
11598/4	(4) 60W G9 (included)	29"	5"	6"	7 lbs.	
11761/3	(3) 60W G9 (included)	13"	13"	-	7 lbs.	




81030/1



81031/2



81032/3



81070/1



81072/3



EPSOM

Polished Chrome finish with white etched glass


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
81030/1	(1) 5W-415 Lumen LED (included)	7"	7"	4"	2 lbs.	ADA Compliant
81031/2	(2) 5W-415 Lumen LED (included)	16"	7"	4"	3 lbs.	ADA Compliant
81032/3	(3) 5W-415 Lumen LED (included)	25"	7"	4"	5 lbs.	ADA Compliant

LINTON

Satin Nickel finish with etched and clear glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
81070/1	(1) 5W-415 Lumen LED (included)	8"	5"	4"	1 lb.	ADA Compliant
81072/3	(3) 5W-415 Lumen LED (included)	18"	5"	4"	3 lbs.	ADA Compliant

*Satin Nickel finish coordinates with Brushed Nickel finish.



54010/1

54011/2

54012/3

LED




54001/2

54000/1



54002/3



54003/4

LED

REILLY

Brushed Nickel finish with solid brushed aluminum light holder

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
54010/1	(1) 5W-450 Lumen LED (integrated)	5"	7"	6"	1 lb.	3000K, 80 CRI
54011/2	(2) 5W-450 Lumen LED (integrated)	14"	5"	8"	1 lb.	3000K, 80 CRI
54012/3	(3) 5W-450 Lumen LED (integrated)	22"	5"	8"	2 lbs.	3000K, 80 CRI

SPIVA

Polished Chrome finish with crystal banding

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
54000/1	(1) 4W-360 Lumen LED (integrated)	5"	6"	7"	1 lb.	3000K, 80 CRI
54001/2	(2) 4W-360 Lumen LED (integrated)	14"	6"	8"	2 lbs.	3000K, 80 CRI
54002/3	(3) 4W-360 Lumen LED (integrated)	21"	6"	8"	3 lbs.	3000K, 80 CRI
54003/4	(4) 4W-360 Lumen LED (integrated)	30"	6"	9"	4 lbs.	3000K, 80 CRI





31163/2



31162/1



31164/3



31165/4



1991/1



1990/3



11228/1



11230/3



11229/2



2993/3



2595/1



CALAIS

Polished Chrome finish clear crystal glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31162/1	(1) 40W G9 (included)	6"	7"	6"	2 lbs.	
31163/2	(2) 40W G9 (included)	13"	7"	7"	3 lbs.	
31164/3	(3) 40W G9 (included)	21"	7"	7"	4 lbs.	
31165/4	(4) 40W G9 (included)	30"	7"	7"	5 lbs.	

OPTIX

Polished Chrome finish with 32% leaded crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1990/3	(3) 60W Cand.	12"	7"	-	4 lbs.	
1991/1	(1) 100W Med.	10"	13"	-	5 lbs.	
2595/1	(1) 60W Cand.	5"	11"	6"	2 lbs.	
2993/3	(3) 60W Cand.	23"	12"	13"	5 lbs.	
11228/1	(1) 60W Cand.	5"	7"	4"	2 lbs.	ADA Compliant
11229/2	(2) 60W Cand.	14"	7"	4"	4 lbs.	ADA Compliant
11230/3	(3) 60W Cand.	21"	7"	4"	6 lbs.	ADA Compliant



11801/2



11800/1



11791/2



11790/1



11802/3



11792/3



11803/4



11793/4



CRYSTAL WAVE

Polished Chrome finish with clear wave patterned glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11800/1	(1) 60W G9 (included)	5"	6"	5"	1 lb.	
11801/2	(2) 60W G9 (included)	14"	5"	5"	3 lbs.	
11802/3	(3) 60W G9 (included)	21"	5"	5"	4 lbs.	
11803/4	(4) 60W G9 (included)	28"	5"	5"	6 lbs.	

LINDALE

Polished Chrome finish with scalloped frosted and clear glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11790/1	(1) 60W G9 (included)	5"	7"	6"	2 lbs.	
11791/2	(2) 60W G9 (included)	13"	5"	6"	3 lbs.	
11792/3	(3) 60W G9 (included)	20"	5"	6"	5 lbs.	
11793/4	(4) 60W G9 (included)	27"	5"	6"	6 lbs.	



31346/1



11225/2



31347/3



17130/1



17131/3



17132/4



CRYSTALLURE

Polished Chrome finish with laser cut shade and square crystal


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11225/2	(2) 60W Med.	13"	8"	-	7 lbs.	Polished Chrome finish
31346/1	(1) 60W Cand.	4"	14"	5"	2 lbs.	
31347/3	(3) 60W Cand.	25"	4"	5"	4 lbs.	

MATRIX

Satin Nickel finish with clear glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17130/1	(1) 40W G9 (included)	4"	4"	5"	2 lbs.	
17131/3	(3) 40W G9 (included)	15"	7"	6"	3 lbs.	
17132/4	(4) 40W G9 (included)	21"	7"	6"	4 lbs.	

*Satin Nickel finish coordinates with Brushed Nickel finish.



46157/2



46156/1



46158/3



10032/3



10030/1



10031/2



CONTOUR

Polished Chrome finish with clear diamond patterned glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
46156/1	(1) 60W G9 (included)	7"	5"	4"	1 lb.	ADA compliant
46157/2	(2) 60W G9 (included)	12"	5"	4"	2 lbs.	
46158/3	(3) 60W G9 (included)	18"	5"	4"	3 lbs.	

ARCHES

Polished Chrome finish with opal white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10030/1	(1) 40W G9 (included)	9"	10"	7"	3 lbs.	
10031/2	(2) 40W G9 (included)	20"	7"	6"	5 lbs.	
10032/3	(3) 40W G9 (included)	30"	7"	6"	7 lbs.	



17081/2



20131/3



66186/2




66185/1



17080/1




17082/3



66187/3



17083/4



66188/4



EASTBROOK

Polished Chrome finish with opal white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17080/1	(1) 40W G9 (included)	7"	6"	4"	2 lbs.	ADA Compliant
17081/2	(2) 40W G9 (included)	18"	7"	4"	3 lbs.	ADA Compliant
17082/3	(3) 40W G9 (included)	29"	7"	4"	5 lbs.	ADA Compliant
17083/4	(4) 40W G9 (included)	40"	7"	4"	6 lbs.	ADA Compliant
20131/3	(3) 60W Med.	16"	6"	-	7 lbs.	Polished Chrome finish

NEW HAVEN

Brushed Nickel with rounded cut corner frosted white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66185/1	(1) 60W Med.	5"	7"	6"	2 lbs.	
66186/2	(2) 60W Med.	14"	6"	6"	4 lbs.	
66187/3	(3) 60W Med.	23"	6"	6"	6 lbs.	
66188/4	(4) 60W Med.	32"	6"	6"	8 lbs.	

*Brushed Nickel finish is the same as our Satin Nickel finish.



7631/2



7633/2



7641/2



7643/2



7632/3



7630/1



7642/3



7640/1



17019/4



17029/4

ELYSBURG

Satin Nickel finish with white marbled glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
7630/1	(1) 60W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended
7631/2	(2) 60W Med.	18"	8"	9"	4 lbs.	G16 1/2 bulbs recommended
7632/3	(3) 60W Med.	25"	10"	9"	5 lbs.	G16 1/2 bulbs recommended
7633/2	(2) 60W Med.	16"	15"	-	6 lbs.	G16 1/2 bulbs recommended
17019/4	(4) 60W Med.	36"	9"	9"	7 lbs.	G16 1/2 bulbs recommended

*Satin Nickel finish coordinates with Brushed Nickel finish.

ELYSBURG

Aged Bronze finish with tea stained brown swirl glass


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
7640/1	(1) 60W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended
7641/2	(2) 60W Med.	18"	8"	9"	4 lbs.	G16 1/2 bulbs recommended
7642/3	(3) 60W Med.	25"	10"	9"	5 lbs.	G16 1/2 bulbs recommended
7643/2	(2) 60W Med.	16"	15"	-	6 lbs.	G16 1/2 bulbs recommended
17029/4	(4) 60W Med.	36"	9"	9"	7 lbs.	G16 1/2 bulbs recommended



17021/2



17020/1



17023/3



17024/4




17641/2



1743/2



17642/3



17640/1



17643/4



ELYSBURG

Polished Chrome finish with white marbled glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17020/1	(1) 60W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended
17021/2	(2) 60W Med.	18"	8"	9"	3 lbs.	G16 1/2 bulbs recommended
17023/3	(3) 60W Med.	25"	10"	9"	5 lbs.	G16 1/2 bulbs recommended
17024/4	(4) 60W Med.	36"	9"	9"	7 lbs.	G16 1/2 bulbs recommended

ELYSBURG

Aged Bronze finish with white marbled glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1743/2	(2) 60W Med.	16"	15"	-	6 lbs.	G16 1/2 bulbs recommended
17640/1	(1) 60W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended
17641/2	(2) 60W Med.	18"	8"	9"	4 lbs.	G16 1/2 bulbs recommended
17642/3	(3) 60W Med.	25"	10"	9"	5 lbs.	G16 1/2 bulbs recommended
17643/4	(4) 60W Med.	36"	9"	9"	7 lbs.	G16 1/2 bulbs recommended



1471/2




1470/1




1471/2CRW



1470/1MAR



1472/3



1472/3CAR



1470/1JAS

REFRACTION

Polished Chrome finish with etched glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1470/1	(1) 40W G9 (included)	7"	5"	9"	1 lb.	
1471/2	(2) 40W G9 (included)	16"	7"	8"	3 lbs.	
1472/3	(3) 40W G9 (included)	25"	7"	8"	4 lbs.	

REFRACTION

Polished Chrome finish with mars, jasper, creme white or caribbean glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1470/1*	(1) 40W G9 (included)	7"	5"	9"	1 lb.	
1471/2*	(2) 40W G9 (included)	16"	7"	8"	3 lbs.	
1472/3*	(3) 40W G9 (included)	25"	7"	8"	4 lbs.	

Refraction fixtures may be purchased in 4 colors in addition to frosted glass. Please indicate color code after item number when ordering.
 MARS=MAR
 JASPER=JAS
 CREME WHITE=CRW
 CARIBBEAN=CAR



14282/3



14281/2



14283/4




14280/1



17053/1



17050/1



17051/2



17052/3



JONAS

Cast metal sockets, pipes, valve wheels with weathered finish and wood accented backplate

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
14280/1	(1) 60W Med.	5"	7"	7"	2 lbs.	Bulb # 1092 optional
14281/2	(2) 60W Med.	12"	8"	6"	4 lbs.	Bulb # 1092 optional
14282/3	(3) 60W Med.	19"	8"	6"	6 lbs.	Bulb # 1092 optional
14283/4	(4) 60W Med.	26"	8"	6"	7 lbs.	Bulb # 1092 optional

RETROSPECTIVES

Polished Chrome finish with opal white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17050/1	(1) 60W Med.	8"	9"	11"	3 lbs.	
17051/2	(2) 60W Med.	18"	9"	11"	5 lbs.	
17052/3	(3) 60W Med.	28"	9"	11"	8 lbs.	
17053/1	(1) 60W Med.	8"	9"	-	3 lbs.	



UTICA

Polished Chrome finish with white blown glass and polished chrome banding


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11415/1	(1) 60W G9 (included)	6"	10"	8"	2 lbs.	
11416/2	(2) 60W G9 (included)	18"	8"	8"	5 lbs.	
11417/3	(3) 60W G9 (included)	29"	8"	8"	7 lbs.	
15015/2	(2) 60W Med.	13"	6"	-	7 lbs.	Polished Chrome finish

NORTHPORT

Satin Nickel finish with opal white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11440/2	(2) 60W Med.	13"	5"	-	4 lbs.	Brushed Nickel finish, opal white glass
17100/1	(1) 100W Med.	5"	8"	7"	2 lbs.	
17101/2	(2) 100W Med.	13"	9"	7"	3 lbs.	
17102/3	(3) 100W Med.	20"	9"	7"	4 lbs.	
17103/4	(4) 100W Med.	28"	9"	7"	5 lbs.	

*Satin Nickel finish coordinates with Brushed Nickel finish.



11401/2



11400/1



11402/3



17261/2



17260/1



17262/3



17263/4



P E M B E R T O N

Brushed Nickel finish with white marbled glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11400/1	(1) 100W Med.	7"	9"	9"	2 lbs.	
11401/2	(2) 100W Med.	18"	9"	9"	4 lbs.	
11402/3	(3) 100W Med.	26"	9"	9"	5 lbs.	

*Brushed Nickel finish is the same as our Satin Nickel finish.

F R E E L A N D

Brushed Nickel finish with opal white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17260/1	(1) 60W Med.	7"	12"	9"	3 lbs.	
17261/2	(2) 60W Med.	17"	7"	8"	4 lbs.	
17262/3	(3) 60W Med.	26"	7"	8"	6 lbs.	
17263/4	(4) 60W Med.	36"	7"	8"	8 lbs.	


*Brushed Nickel finish is the same as our Satin Nickel finish.



11436/1



11475/1



11437/2



11438/3



10071/2



10070/1



10072/3

SERENITY

Oiled Bronze finish with tan cubic glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11436/1	(1) 60W G9 (included)	5"	7"	6"	2 lbs.	
11437/2	(2) 60W G9 (included)	13"	7"	6"	4 lbs.	
11438/3	(3) 60W G9 (included)	23"	7"	6"	5 lbs.	
11475/1	(1) 60W G9 (included)	10"	10"	5"	3 lbs.	

REFLECTIONS

Polished Chrome finish with polished chrome glass which is opaque when not lit

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10070/1	(1) 60W Med.	5"	8"	7"	2 lbs.	
10071/2	(2) 60W Med.	18"	8"	8"	3 lbs.	
10072/3	(3) 60W Med.	23"	8"	8"	4 lbs.	



11265/2



11465/3



11266/3



11264/1



11267/4



11681/2



11680/1



11682/3



11683/4

BRYANT

Satin Nickel finish with opal white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11264/1	(1) 100W Med.	5"	9"	6"	3 lbs.	
11265/2	(2) 100W Med.	14"	9"	6"	4 lbs.	
11266/3	(3) 100W Med.	23"	9"	6"	6 lbs.	
11267/4	(4) 100W Med.	32"	9"	6"	7 lbs.	
11465/3	(3) 60W Med.	15"	5"	-	7 lbs.	Brushed Nickel finish, opal white glass

*Satin Nickel finish coordinates with Brushed Nickel finish.

JAYDEN

Polished Chrome finish with ribbed frosted glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11680/1	(1) 100W Med.	5"	9"	6"	4 lbs.	
11681/2	(2) 100W Med.	13"	10"	6"	6 lbs.	
11682/3	(3) 100W Med.	21"	10"	6"	9 lbs.	
11683/4	(4) 100W Med.	29"	10"	6"	11 lbs.	

52001/2



52000/1

52011/2



52010/1

52002/3



52012/3



52003/4



52013/4



ACADIA

Brushed Nickel finish with opal white reeded pressed glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
52000/1	(1) 100W Med.	5"	10"	7"	3 lbs.	
52001/2	(2) 100W Med.	13"	10"	7"	6 lbs.	
52002/3	(3) 100W Med.	22"	10"	7"	9 lbs.	
52003/4	(4) 100W Med.	30"	10"	7"	11 lbs.	

ACADIA

Oil Rubbed Bronze finish with amber reeded pressed glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
52010/1	(1) 100W Med.	5"	10"	7"	3 lbs.	
52011/2	(2) 100W Med.	13"	10"	7"	6 lbs.	
52012/3	(3) 100W Med.	22"	10"	7"	9 lbs.	
52013/4	(4) 100W Med.	30"	10"	7"	11 lbs.	



11661/2


11660/1




11671/2


11670/1





11662/3





11672/3




11663/4




11673/4


DAWSON

Brushed Nickel finish with opal white blown glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11660/1	(1) 100W Med.	5"	10"	6"	3 lbs.	
11661/2	(2) 100W Med.	15"	10"	6"	5 lbs.	
11662/3	(3) 100W Med.	23"	10"	6"	7 lbs.	
11663/4	(4) 100W Med.	31"	10"	6"	9 lbs.	

DAWSON

Oil Rubbed Bronze finish with opal white blown glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11670/1	(1) 100W Med.	5"	10"	6"	3 lbs.	
11671/2	(2) 100W Med.	15"	10"	6"	5 lbs.	
11672/3	(3) 100W Med.	23"	10"	6"	7 lbs.	
11673/4	(4) 100W Med.	31"	10"	6"	9 lbs.	



11590/1



11580/1

BRISTOL WAY

Oil Rubbed Bronze finish with opal white blown glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11590/1	(1) 100W Med.	5"	10"	6"	2 lbs.	
11591/2	(2) 100W Med.	13"	10"	6"	4 lbs.	
11592/3	(3) 100W Med.	21"	10"	6"	5 lbs.	
11593/4	(4) 100W Med.	29"	10"	6"	7 lbs.	

BRISTOL WAY

Brushed Nickel finish with opal white blown glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11580/1	(1) 100W Med.	5"	10"	6"	2 lbs.	
11581/2	(2) 100W Med.	13"	10"	6"	4 lbs.	
11582/3	(3) 100W Med.	21"	10"	6"	5 lbs.	
11583/4	(4) 100W Med.	29"	10"	6"	7 lbs.	



66211-1



66212-2



66221-1



Lamp arm swivels to up or down position

66213-3



66214-4



11601/2



11600/1



11602/3



11603/4



QUINTON PARLOR

Oiled Bronze finish with white hand-blown glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66211-1	(1) 60W Med.	5"	12"	7"	2 lbs.	Lamp arm swivels to up or down position
66212-2	(2) 60W Med.	13"	12"	9"	4 lbs.	Lamp arm swivels to up or down position
66213-3	(3) 60W Med.	20"	12"	9"	5 lbs.	Lamp arm swivels to up or down position
66214-4	(4) 60W Med.	29"	12"	9"	7 lbs.	Lamp arm swivels to up or down position
66221-1	(1) 75W Med.	11"	11"	-	3 lbs.	

SMITHFIELD

Brushed Nickel finish with opal white blown glass shades and brushed nickel banding

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11600/1	(1) 60W Med.	6"	12"	8"	3 lbs.	Shades included
11601/2	(2) 60W Med.	16"	13"	8"	4 lbs.	Shades included
11602/3	(3) 60W Med.	25"	13"	8"	7 lbs.	Shades included
11603/4	(4) 60W Med.	34"	13"	8"	8 lbs.	Shades included



11641/2



11640/1



11651/2



11654/2



11642/3



11652/3



11650/1



11643/4



11653/4

PARK RIDGE

Polished Nickel finish with reeded opal white blown glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11640/1	(1) 60W Med.	5"	9"	8"	2 lbs.	
11641/2	(2) 60W Med.	11"	9"	8"	4 lbs.	
11642/3	(3) 60W Med.	19"	9"	8"	5 lbs.	
11643/4	(4) 60W Med.	26"	9"	8"	7 lbs.	

PARK RIDGE

Oil Rubbed Bronze finish with reeded light amber blown glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11650/1	(1) 60W Med.	5"	9"	8"	2 lbs.	
11651/2	(2) 60W Med.	11"	9"	8"	4 lbs.	
11652/3	(3) 60W Med.	19"	9"	8"	5 lbs.	
11653/4	(4) 60W Med.	26"	9"	8"	7 lbs.	
11654/2	(2) 60W Med.	13"	11"	-	4 lbs.	



11440/2



20131/3



67021-2



67020-1



67011-2



67010-1



67022-3



67012-3



BERWICK

Brushed Nickel finish with white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11440/2	(2) 60W Med.	13"	5"	-	4 lbs.	Brushed Nickel finish, opal white glass
67020-1	(1) 100W Med.	7"	8"	9"	2 lbs.	
67021-2	(2) 100W Med.	17"	8"	9"	4 lbs.	
67022-3	(3) 100W Med.	27"	8"	9"	6 lbs.	

*Brushed Nickel finish is the same as our Satin Nickel finish.

BERWICK

Polished Chrome finish with white glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
20131/3	(3) 60W Med.	16"	6"	-	7 lbs.	Polished Chrome finish
67010-1	(1) 100W Med.	7"	8"	9"	2 lbs.	
67011-2	(2) 100W Med.	17"	8"	9"	4 lbs.	
67012-3	(3) 100W Med.	27"	8"	9"	6 lbs.	



Satin Nickel finish



Satin Nickel bars shown with Snow White glass (SW)



Aged Bronze finish



Polished Chrome finish



Aged Bronze bars shown with Espresso glass (ES)



Polished Chrome bars shown with Multi glass (M)


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
570/1B*	(1) 75W Med.	5"	10"	8"	2 lbs.	Aged Bronze finish
570/2B*	(2) 75W Med.	14"	7"	8"	4 lbs.	Aged Bronze finish
570/3B*	(3) 75W Med.	20"	7"	8"	5 lbs.	Aged Bronze finish
570/4B*	(4) 75W Med.	27"	7"	8"	8 lbs.	Aged Bronze finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
570/1N*	(1) 75W Med.	5"	10"	8"	2 lbs.	Satin Nickel finish
570/2N*	(2) 75W Med.	14"	7"	8"	4 lbs.	Satin Nickel finish
570/3N*	(3) 75W Med.	20"	7"	8"	5 lbs.	Satin Nickel finish
570/4N*	(4) 75W Med.	27"	7"	8"	8 lbs.	Satin Nickel finish
570/1C*	(1) 75W Med.	5"	10"	8"	2 lbs.	Polished Chrome finish
570/2C*	(2) 75W Med.	14"	7"	8"	4 lbs.	Polished Chrome finish
570/3C*	(3) 75W Med.	20"	7"	8"	5 lbs.	Polished Chrome finish
570/4C*	(4) 75W Med.	27"	7"	8"	8 lbs.	Polished Chrome finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* When ordering, please include glass color code after item number.

**Satin Nickel finish coordinates with Brushed Nickel finish.



11200/1




11201/3

L I N C O L N S Q U A R E

Polished Nickel finish with hand-cut crystal elements and crystalline glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11200/1	(1) 75W Med.	6"	10"	8"	2 lbs.	
11201/3	(3) 75W Med.	28"	9"	8"	8 lbs.	



2156/2



2151/2



2157/3



2152/3



2150/1




2153/4

R E G E N C Y

Burnt Bronze finish with weathered gold leaf accents and caramel amber glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2150/1	(1) 75W Med.	6"	18"	7"	5 lbs.	
2151/2	(2) 75W Med.	20"	11"	8"	7 lbs.	
2152/3	(3) 75W Med.	30"	11"	8"	10 lbs.	
2153/4	(4) 75W Med.	39"	11"	8"	12 lbs.	
2156/2	(2) 60W Med.	16"	10"	-	9 lbs.	
2157/3	(3) 60W Med.	19"	20"	-	16 lbs.	



LAWRENCEVILLE

Mocha finish with antique amber glass


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
9319/2	(2) 60W Med.	16"	9"	-	5 lbs.	
9320/1	(1) 75W Med.	6"	13"	7"	1 lb.	
9321/2	(2) 75W Med.	16"	10"	7"	3 lbs.	
9322/3	(3) 75W Med.	24"	10"	7"	6 lbs.	

CHELSEA

Aged Silver finish with crystal accents and amber glass

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
3820/2	(2) 60W Cand.	20"	11"	8"	5 lbs.	
3821/3	(3) 60W Cand.	30"	11"	8"	7 lbs.	
3822/4	(4) 60W Cand.	39"	11"	8"	10 lbs.	
3823/1	(1) 60W Cand.	5"	19"	8"	3 lbs.	
3825/3	(3) 60W Cand.	17"	14"	-	4 lbs.	

7046/3



7044/3



7040/2



18096/3



18093/1



7042/3



7050/1



18094/3



20075/3



CRISTALLO FIORE

Deep Rust finish with hand-blown glass florets and drops of amber and clear crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
7040/2	(2) 100W Med.	18"	11"	9"	7 lbs.	
7042/3	(3) 100W Med.	26"	11"	9"	10 lbs.	
7044/3	(3) 60W Cand.	19"	13"	-	8 lbs.	
7046/3	(3) 60W Cand.	27"	12"	-	7 lbs.	
7050/1	(1) 100W Med.	6"	14"	9"	3 lbs.	
20075/3	(3) 60W Cand.	30"	8"	6"	4 lbs.	

HERITAGE

Cream finish with porcelain pink roses and pink crystal

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
18093/1	(1) 60W Cand.	7"	12"	6"	2 lbs.	
18094/3	(3) 60W Cand.	27"	11"	6"	4 lbs.	
18096/3	(3) 60W Cand.	17"	8"	-	6 lbs.	



MINI PENDANTS

Stylish Task Oriented Lighting



10242/1AQ Aqua
10242/1CL Clear
10242/1SM Smoke

ICE FRAGMENTS

10245/1
10246/1

ETCHED GLASS

10331/1CLR Hammered Clear
10331/1HAMB Hammered Amber
10331/1HAQ Hammered Aqua
10331/1HRD Hammered Red

HAMMERED GLASS *Bulb #1092 optional



10431/1CLR Hammered Clear
10431/1HAQ Hammered Aqua
10431/1HAMP Hammered Amber Plated
10431/1HME Hammered Mercury

HAMMERED GLASS *Bulb #1092 optional

10332/1
*Bulb #1092 optional

HAMMERED GLASS

10243/1FA Frosted Aqua
10243/1FC Frosted Clear
10243/1FSM Frosted Smoke

SYNTHESIS

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10242/1AQ	(1) 60W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10242/1CL	(1) 60W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10242/1SM	(1) 60W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10245/1	(1) 100W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10246/1	(1) 100W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of white cord, White finish
10431/1CLR	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10431/1HAQ	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10431/1HAMP	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
10431/1HME	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10243/1FA	(1) 60W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10243/1FC	(1) 60W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10243/1SM	(1) 60W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10331/1CLR	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of cord, Oil Rubbed Bronze finish
10331/1HAMB	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of cord, Oil Rubbed Bronze finish
10331/1HAQ	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of cord, Oil Rubbed Bronze finish
10331/1HRD	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of cord, Oil Rubbed Bronze finish
10332/1	(1) 60W Med.	9"	5"	79"	2 lbs.	Includes 6 feet of cord, Oil Rubbed Bronze finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



60042-1 60043-1 60045-1 60047-1 60052-1 60053-1 60055-1 60057-1



60066-1 60044-1 60046-1 60054-1 60056-1 60065-1 60064-1

MENLOW PARK *Bulb #1092 optional

MENLOW PARK *Bulb #1092 optional

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
60042-1	(1) 60W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60043-1	(1) 60W Med.	6"	11"	85"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60044-1	(1) 60W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60045-1	(1) 75W Med.	8"	16"	90"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60046-1	(1) 60W Med. (included)	2"	3"	77"	1 lb.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60047-1	(1) 60W Med.	6"	9"	83"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
60066-1	(1) 60W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
60052-1	(1) 60W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60053-1	(1) 60W Med.	6"	11"	85"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60054-1	(1) 60W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60055-1	(1) 75W Med.	8"	16"	90"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60056-1	(1) 60W Med. (included)	2"	3"	77"	1 lb.	Includes 6 feet of clear cord, Polished Chrome finish
60057-1	(1) 60W Med.	6"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60064-1	(1) 60W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
60065-1	(1) 75W Med.	8"	16"	90"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



10423/1
Clear



10422/1
Clear



10433/1
Amber Teak



10432/1
Amber Teak



10435/1
Clear



10436/1
Rustic Mercury



10437/1
Clear Sugar



10438/1
Spotted Mercury



ORBITAL *Bulb #1092 optional

HAND FORMED GLASS



10424/1
Clear



10434/1
Smoke



46005/1



17205/1



ORBITAL

SKYLAR

CIPHER



10440/1
Clear



10441/1
Clear



10450/1
Amber Teak



10451/1
Amber Teak



GEOMETRICS *Bulb #1092 optional

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10422/1	(1) 60W Med.	10"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10423/1	(1) 60W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10424/1	(1) 60W Med.	8"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10432/1	(1) 60W Med.	10"	12"	86"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
10433/1	(1) 60W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
10434/1	(1) 60W Med.	8"	7"	81"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
17205/1	(1) 75W Med.	7"	16"	90"	4 lbs.	Bulb #1099 optional, Oil Rubbed Bronze finish
46005/1	(1) 60W Med.	5"	11"	85"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10435/1	(1) 60W Med.	10"	9"	83"	4 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
10436/1	(1) 60W Med.	10"	9"	55"	4 lbs.	Includes 18" of chain, 2 feet rope, Oil Rubbed Bronze finish
10437/1	(1) 60W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
10438/1	(1) 60W Med.	7"	12"	56"	3 lbs.	Includes 18" of chain, 2 feet rope, Oil Rubbed Bronze finish
10440/1	(1) 60W Med.	9"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10441/1	(1) 60W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10450/1	(1) 60W Med.	9"	8"	82"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
10451/1	(1) 60W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)





46014/1



46017/1



46018/1



46019/1



46010/1



46000/1



DARIEN



46171/1
Clear



46170/1
Clear




DUNCAN

*Bulb #1092 optional



46172/1
Antique Mercury



46024/1



46007/1



46023/1



46008/1



46009/1



DANICA

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
46007/1	(1) 60W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
46008/1	(1) 60W Med.	8"	9"	83"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
46009/1	(1) 100W Med.	5"	10"	84"	3 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
46014/1	(1) 100W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46017/1	(1) 60W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46018/1	(1) 60W Med.	8"	9"	83"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46019/1	(1) 100W Med.	5"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46023/1	(1) 50W Par 20	5"	6"	80"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
46024/1	(1) 100W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish




31080/1AMB
Amber



31080/1CLR
Clear



VIVA



31080/1GRN
Green



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
31080/1AMB	(1) 100W Med.	7"	7"	81"	2 lbs	Includes 6 feet of clear cord, Polished Chrome finish
31080/1CLR	(1) 100W Med.	7"	7"	81"	2 lbs	Includes 6 feet of clear cord, Polished Chrome finish
31080/1GRN	(1) 100W Med.	7"	7"	81"	2 lbs	Includes 6 feet of clear cord, Polished Chrome finish
46000/1	(1) 60W Med.	6"	7"	81"	1 lb.	Includes 6 feet of brown cord, Oiled Bronze finish
46010/1	(1) 60W Med.	6"	7"	81"	1 lb.	Includes 6 feet of clear cord, Polished Chrome finish
46170/1	(1) 60W Med.	6"	11"	84"	2 lbs.	Includes 6 feet of brown cord, Antique Gold Leaf finish
46171/1	(1) 60W Med.	6"	11"	84"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46172/1	(1) 60W Med.	6"	11"	84"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)





31380/1CMP
Champagne



WATERSPHERE



31380/1SMK
Smoke



10333/1



RIBBED GLASS



Shown with
light off



10247/1
Mercury



RURY



31148/1



ENCAPSULATE



31143/1



CUBICO



10240/1CHR
Chrome



Shown with
light off

CASSANDRA



10240/1WH
White



10248/1
Mercury



JERARD



10249/1
Amber Teak



MICKLEY



10464/1
Clear with Frosted Inner Glass



LAYERS



10474/1
Amber Teak with Frosted Inner Glass



46107/1



STRATA



46161/1



CARVED GLASS



46162/1



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10247/1	(1) 60W Med.	4"	13"	85"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10248/1	(1) 60W Med.	5"	15"	88"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
10249/1	(1) 60W Med.	6"	13"	87"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10333/1	(1) 60W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10464/1	(1) 60W Med.	6"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10474/1	(1) 60W Med.	6"	9"	83"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
31380/1CMP	(1) 100W Med.	10"	11"	85"	4 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
31380/1SMK	(1) 100W Med.	10"	11"	85"	4 lbs.	Includes 6 feet of clear cord, Polished Chrome finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10240/1CHR	(1) 100W Med.	8"	9"	83"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10240/1WH	(1) 100W Med.	8"	9"	83"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
31143/1	(1) 40W G9 (included)	3"	5"	79"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31148/1	(1) 40W G9 (included)	4"	8"	82"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
46107/1	(1) 100W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46161/1	(1) 40W G9 (included)	4"	6"	80"	2 lbs.	Includes 6 feet of clear cord, Brushed Nickel finish
46162/1	(1) 40W G9 (included)	4"	6"	80"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)





31078/1



31077/1



31076/1



CHROMIA



1477/1



REFRACTION




31445/1RB
Rainbow Streak



31445/1TB
Tropics



COLORWAVE



31539/1CG
Cream/Green



SURREAL



31339/1



SURREALIST



1477/1CAR
Caribbean



1477/1CRW
Creme White



REFRACTION



1477/1JAS
Jasper



1477/1MAR
Mars



31616/1
Sunscape



31617/1
Shadow




DUNES



31615/1



CANYON



31495/1



HORIZON

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
1477/1	(1) 40W G9 (included)	7"	4"	78"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
1477/1CAR	(1) 40W G9 (included)	7"	4"	78"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
1477/1CRW	(1) 40W G9 (included)	7"	4"	78"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
1477/1JAS	(1) 40W G9 (included)	7"	4"	78"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
1477/1MAR	(1) 40W G9 (included)	7"	4"	78"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
31076/1	(1) 100W Med.	5"	9"	83"	2 lbs.	Polished Chrome finish, Includes 6 feet of clear cord
31077/1	(1) 100W Med.	4"	9"	83"	2 lbs.	Polished Chrome finish, Includes 6 feet of clear cord
31078/1	(1) 100W Med.	4"	12"	86"	2 lbs.	Polished Chrome finish, Includes 6 feet of clear cord

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
31339/1	(1) 100W Med.	5"	9"	83"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
31445/1RB	(1) 60W Med.	6"	7"	81"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31445/1TB	(1) 60W Med.	6"	7"	81"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31495/1	(1) 100W Med.	5"	10"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31539/1CG	(1) 60W Med.	5"	8"	82"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31615/1	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31616/1	(1) 100W Med.	6"	9"	81"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31617/1	(1) 100W Med.	6"	9"	81"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



10467/1WH
White



10467/1AQ
Aqua



10467/1CL
Clear



10477/1
Clear



TEARDROP *(1) 6" & (2) 12" extension rods w/hang straight included



10330/1TB
Textured Beige



ANDOVER

10147/1



COLETTA
Genuine Stone

10169/1




PIEDRA
Genuine Stone

551-1MA
Maple Amber



MAPLE

551-1MD
Maple Dusk



2583/1
Cardinal Red



2581/1
Royal Blue



2582/1
Tobacco



2580/1
White



545-1SAH
Sahara



VESTA

DESERT WINDS



10466/1



SANDSTORM

10476/1



10143/1PB
Pebbled Blue



CIRA

10143/1PW
Pebbled Gray-White



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
545-1SAH	(1) 75W Med.	5"	17"	91"	4 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
2580/1	(1) 75W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
2581/1	(1) 75W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
2582/1	(1) 75W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
2583/1	(1) 75W Med.	5"	12"	86"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10467/1AQ	(1) 60W Cand.	4"	15"	47"	2 lbs.	Satin Nickel finish
10467/1CL	(1) 60W Cand.	4"	15"	47"	2 lbs.	Satin Nickel finish
10467/1WH	(1) 60W Cand.	4"	15"	47"	2 lbs.	Satin Nickel finish
10477/1	(1) 60W Cand.	4"	15"	47"	2 lbs.	Oil Rubbed Bronze finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
551-1MA	(1) 75W Med.	4"	13"	87"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
551-1MD	(1) 75W Med.	4"	13"	87"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10143/1PB	(1) 100W Med.	6"	6"	80"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10143/1PW	(1) 100W Med.	6"	6"	80"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10147/1	(1) 60W Med.	4"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10169/1	(1) 60W Med.	4"	8"	82"	4 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10330/1TB	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10466/1	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
10476/1	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



VINES

FUSION



TWISTER

PREDATOR

GEMSTONES

CAPRI Capiz Shells

CRACKLE

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
542-1	(1) 100W Med.	6"	8"	82"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10445/1	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31142/1	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31348/1MN	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31338/1VINW	(1) 75W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
31658/1	(1) 100W Med.	5"	9"	80"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31668/1	(1) 100W Med.	5"	8"	80"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
528-1CPR	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
528-1GLD	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
528-1MLT	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
528-1SLV	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
528-1WHT	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10141/1	(1) 75W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10142/1	(1) 75W Med.	6"	11"	85"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10442/1	(1) 60W Med.	5"	10"	86"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31376/1	(1) 100W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



10412/1
Multi Shells



10415/1
Multi Bunched Shells



10416/1
Multi Bunched Shells



10414/1
Ribbed Shells



SHELLS



10465/1BRF
Smoke



10465/1SVF
Silver



FISSURE



10208/1CLD
Cloud



10208/1SLV
Silver



FISSION



10208/1WN
Wine




20000/1



SEASHORE
Hand-Painted



10419/1
Multi



GLASS MOSAIC




10429/1
Fuschia



546-1RBY-CRC
Ruby



546-1SLV-CRC
Silver



CURVALO



546-1SLVM-CRC
Silver Multi



10144/1FS



FIRESTORM

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10412/1	(1) 60W Med.	5"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10414/1	(1) 60W Med.	6"	8"	82"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10415/1	(1) 60W Med.	6"	8"	82"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10416/1	(1) 60W Med.	6"	8"	82"	3 lbs.	Includes 6 feet of white cord, Matte White finish
10419/1	(1) 60W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10429/1	(1) 60W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
20000/1	(1) 100W Med.	7"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
546-1RBY-CRC	(1) 100W Med.	6"	13"	87"	4 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
546-1SLV-CRC	(1) 100W Med.	6"	13"	87"	4 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
546-1SLVM-CRC	(1) 100W Med.	6"	13"	87"	4 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10144/1FS	(1) 100W Med.	7"	7"	81"	3 lbs.	Includes 6 feet of black cord, Oil Rubbed Bronze finish
10208/1CLD	(1) 100W Med.	5"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10208/1SLV	(1) 100W Med.	5"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10208/1WN	(1) 100W Med.	5"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10465/1BRF	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
10465/1SVF	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish


Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



10220/1EMB Ember
10220/1FBR Firebrick
10220/1SUN Sunset
31147/1
10254/1
31538/1
31137/1
31138/1

MAUI | **COLLAGE** | **KARMA** | **GARDEN BREEZE** | **SANDSTONE** | **GRANITE**



10256/1
10255/1
10253/1BC Burnt Caramel
10253/1CL Clear
10460/1CS Cosmic Storm
10460/1LS Lava Sunrise
10460/1SF Solar Flare
10077/1

VENTURE | **GEVAL** | **ABSTRACTIONS** | **GEOLOGIC**

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10220/1EMB	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10220/1FBR	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10220/1SUN	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10253/BC	(1) 60W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10253/CL	(1) 60W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
10255/1	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
10256/1	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
31147/1	(1) 100W Med.	4"	8"	82"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10077/1	(1) 100W Med.	6"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10254/1	(1) 60W Med.	5"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10460/1CS	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
10460/1LS	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
10460/1SF	(1) 60W Med.	5"	7"	81"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
31137/1	(1) 100W Med.	5"	11"	85"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31138/1	(1) 100W Med.	7"	10"	84"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31538/1	(1) 100W Med.	6"	10"	84"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



527-1A
Autumn



527-1CR
Creme



527-1CY
Candy



527-1SY
Sandy



PIERRA



10076/1GI
Golden



10076/1SBI
Storm Blue



IRIDESCENCE



31133/1ASH
Ashflow



31133/1PLN
Planetary



FORMATIONS



10222/1COC
Coconut



FAVELA



10223/1COC
Coconut



FAVELITA



10223/1MEL
Honey Melon



544-1MO
Molten Ocean



MOLTEN



10079/1RV
Rainbow



VORTEX



10089/1EVG
Evergreen



MINI VORTEX



10089/1RV
Rainbow



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
527-1A	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
527-1CR	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
527-1CY	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
527-1SY	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10222/1COC	(1) 75W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10223/1COC	(1) 60W Cand.	3"	6"	80"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
10223/1MEL	(1) 60W Cand.	3"	6"	80"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
544-1MO	(1) 100W Med.	5"	11"	85"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10076/1GI	(1) 60W Cand.	5"	11"	85"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10076/1SBI	(1) 60W Cand.	5"	11"	85"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10079/1RV	(1) 100W Med.	5"	12"	86"	4 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10089/1EVG	(1) 100W Med.	4"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10089/1RV	(1) 100W Med.	4"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31133/1ASH	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31133/1PLN	(1) 100W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



20001/1BG
Brown



20001/1CG
Creamy Mint



20001/1MG
Misty Lavender



20001/1RG
Red



20001/1SG
Smoke



GALAXY



522-1C
Cocoa



522-1M
Multi



522-1SC
Scarlet



522-1WS
White Swirl



CILINDRO



Shown with light off

Shown with light off

31600/1
Seagrass



31610/1
Ruby



31620/1
Seafoam



31630/1
Amber



TIDEWATERS



517-1S
Sapphire



517-1C
Cocoa



517-1SC
Scarlet



517-1M
Multi



517-1WS
White Swirl



MULINELLO

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
20001/1BG	(1) 75W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
20001/1CG	(1) 75W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
20001/1MG	(1) 75W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
20001/1RG	(1) 75W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
20001/1SG	(1) 75W Med.	5"	9"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31600/1	(1) 100W Med.	5"	10"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31610/1	(1) 100W Med.	5"	10"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31620/1	(1) 100W Med.	5"	10"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31630/1	(1) 100W Med.	5"	10"	83"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
517-1C	(1) 100W Med.	6"	11"	85"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
517-1M	(1) 100W Med.	6"	11"	85"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
517-1S	(1) 100W Med.	6"	11"	85"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
517-1SC	(1) 100W Med.	6"	11"	85"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
517-1WS	(1) 100W Med.	6"	11"	85"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
522-1C	(1) 100W Med.	4"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
522-1M	(1) 100W Med.	4"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
522-1SC	(1) 100W Med.	4"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
522-1WS	(1) 100W Med.	4"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



416-1CN
Canary



416-1C
Cocoa



416-1M
Multi



110-1ES
Espresso



110-1FR
Fire Red



110-1MT
Mountain



110-1WH
Simple White



416-1S
Sapphire



416-1SC
Scarlet



416-1WS
White Swirl



110-1SW
Snow White



110-1BL
Starburst Blue



110-1YW
Yellow Blaze



ARCO BALENO

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
416-1C	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
416-1CN	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
416-1M	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
416-1S	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
416-1SC	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
416-1WS	(1) 100W Med.	5"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

MILAN

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
110-1BL	(1) 60W Cand.	3"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
110-1ES	(1) 60W Cand.	3"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
110-1FR	(1) 60W Cand.	3"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
110-1MT	(1) 60W Cand.	3"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
110-1SW	(1) 60W Cand.	3"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
110-1WH	(1) 60W Cand.	3"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
110-1YW	(1) 60W Cand.	3"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



406-1FR
Fire Red



406-1ES
Espresso



406-1MT
Mountain



406-1WH
Simple White




502-1ES
Espresso



502-1FR
Fire Red



502-1SW
Snow White



502-1BL
Starburst Blue



502-1YW
Yellow Blaze



VERONA



406-1SW
Snow White



406-1BL
Starburst Blue



406-1YW
Yellow Blaze



CLASSICO



501-1ES
Espresso



501-1FR
Fire Red



501-1SW
Snow White



LUNGO

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
406-1BL	(1) 100W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of black cord, Oil Rubbed Bronze finish
406-1ES	(1) 100W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of black cord, Oil Rubbed Bronze finish
406-1FR	(1) 100W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of black cord, Oil Rubbed Bronze finish
406-1MT	(1) 100W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of black cord, Oil Rubbed Bronze finish
406-1SW	(1) 100W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of black cord, Oil Rubbed Bronze finish
406-1WH	(1) 100W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of black cord, Oil Rubbed Bronze finish
406-1YW	(1) 100W Med.	5"	7"	81"	3 lbs.	Includes 6 feet of black cord, Oil Rubbed Bronze finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
501-1ES	(1) 60W Cand.	3"	13"	87"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
501-1FR	(1) 60W Cand.	3"	13"	87"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
501-1SW	(1) 60W Cand.	3"	13"	87"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
502-1BL	(1) 100W Med.	5"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
502-1ES	(1) 100W Med.	5"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
502-1FR	(1) 100W Med.	5"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
502-1SW	(1) 100W Med.	5"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
502-1YW	(1) 100W Med.	5"	12"	86"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.



101-1ES
Espresso



101-1FR
Fire Red



101-1MT
Mountain



101-1SW
Snow White



MELA



10455/1



10457/1



10456/1



10458/1



101-1BL
Starburst Blue




101-1YW
Yellow Blaze



MELA



10421/1JD
Jade



10421/1TS
Frosted



MELONY



10341/1



10342/1



KERSEY



10343/1



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
101-1BL	(1) 60W Med.	6"	6"	80"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
101-1ES	(1) 60W Med.	6"	6"	80"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
101-1FR	(1) 60W Med.	6"	6"	80"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
101-1MT	(1) 60W Med.	6"	6"	80"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
101-1SW	(1) 60W Med.	6"	6"	80"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
101-1YW	(1) 60W Med.	6"	6"	80"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
10421/1JD	(1) 40W G9 (included)	4"	5"	79"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10421/1TS	(1) 40W G9 (included)	4"	5"	79"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
10341/1	(1) 40W G9 (included)	5"	6"	80"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10342/1	(1) 40W G9 (included)	5"	6"	80"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10343/1	(1) 60W Med.	4"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10455/1	(1) 40W G9 (included)	5"	6"	80"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10456/1	(1) 40W G9 (included)	5"	6"	80"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10457/1	(1) 40W G9 (included)	4"	7"	81"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
10458/1	(1) 60W Cand.	4"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)





31486/1
31487/1
31488/1
31489/1

CYNTHIA



17042/1ALM
17210/1
17220/1
17200/1

SPUN ALUMINUM

SORENSEN



17165/1
46180/1
46181/1
46182/1

WATERCUBE Bulb #1092 optional
(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included



17196/1
17195/1
17170/1
20064/1
17190/1

CHAPEAU

VASSO CHROMO

NESTOR

ROXA

LED
ALEA

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
17165/1	(1) 5W-600 Lumen LED (included)	3"	5"	79"	2 lbs.	3200K, 80 CRI, Polished Chrome finish
31486/1	(1) 60W Cand.	3"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
31487/1	(1) 60W Cand.	3"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
31488/1	(1) 60W Cand.	4"	8"	82"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
31489/1	(1) 60W Cand.	5"	8"	82"	3 lbs.	Includes 6 feet of clear cord, Polished Chrome finish
46180/1	(1) 60W Med.	5"	8"	46"	2 lbs.	Antique Gold Leaf finish, clear glass
46181/1	(1) 60W Med.	5"	8"	46"	2 lbs.	Polished Chrome finish, clear glass
46182/1	(1) 60W Med.	5"	8"	46"	2 lbs.	Oil Rubbed Bronze finish, teak glass

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
17042/1ALM	(1) 60W Cand.	7"	10"	84"	1 lb.	Includes 6 feet of clear cord, Satin Nickel finish
17170/1	(1) 5W-700 Lumen LED (included)	4"	9"	82"	1 lb.	3200K, 80 CRI, Polished Chrome finish
17190/1	(1) 100W Med.	12"	13"	87"	2 lbs.	Etched Stainless Steel with Polished Chrome hardware
17195/1	(1) 75W Med.	10"	8"	82"	3 lbs.	Matte Black finish
17196/1	(1) 75W Med.	10"	10"	84"	3 lbs.	Matte Black finish
17200/1	(1) 75W Med.	10"	12"	86"	2 lbs.	Oil Rubbed Bronze finish
17210/1	(1) 75W Med.	10"	12"	86"	2 lbs.	Gloss Black finish
17220/1	(1) 75W Med.	10"	12"	86"	2 lbs.	Gloss White finish
20064/1	(1) 100W Med.	8"	13"	87"	5 lbs.	Includes 6 feet of clear cord, Polished Chrome finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* Please see pages 622-627 for pendant hanging options. (Pendants shown here for example only)



LED Option LED option available. When ordering include -LED after item number.

PENDANT OPTIONS

3 LIGHT TRIANGULAR

When ordering triangular pan only, use item number below. When ordering with pendants, use item number of single pendant + /3 (for 3 light pan) + color code of glass (if applicable). See item numbers of 3 light pendants on this page as examples.



3T-SN



3T-OB



3T-CHR

ITEM NO.	W	WEIGHT	ADDITIONAL DETAILS
3T-CHR	10"	1 lb.	Polished Chrome finish
3T-OB	10"	1 lb.	Oiled Bronze finish
3T-SN	10"	1 lb.	Satin Nickel finish



416-3M



10331/3HAMB



20064/3

3 LIGHT LINEAR

When ordering linear bar only, use item number below. When ordering with pendants, use item number of single pendant + /3L (for 3 light linear bar) + color code of glass (if applicable). See item numbers of 3 light linear pendants on this page as examples.



3L-SN



3L-OB



3L-CHR

ITEM NO.	W	WEIGHT	ADDITIONAL DETAILS
3L-CHR	36"	2 lbs.	Polished Chrome finish
3L-OB	36"	2 lbs.	Oiled Bronze finish
3L-SN	36"	2 lbs.	Satin Nickel finish



528-3L-SLV



46008/3L



31078/3L


6 LIGHT RECTANGULAR

When ordering pan only, use item number below. When ordering with pendants, use item number of single pendant + /6rc (for 6 light rectangular pan) + color code of glass (if applicable). See item numbers of 6 light pendants on this page as examples.

6RC-SN





6RC-OB

6RC-CHR




ITEM NO.	W	WEIGHT	ADDITIONAL DETAILS
6RC-CHR	30"x9"	2 lbs.	Polished Chrome finish
6RC-OB	30"x9"	2 lbs.	Oiled Bronze finish
6RC-SN	30"x9"	2 lbs.	Satin Nickel finish



10077/6RC




60047-6RC




60053-6RC


6 LIGHT H BAR

When ordering H bar only, use item number below. When ordering with pendants, use item number of single pendant + /6 (for 6 light H bar) + color code of glass (if applicable). See item numbers of 6 light pendants on this page as examples.
 Note: This item does not come in Polished Chrome, but Satin Nickel can be used to coordinate with Chrome hardware pendants.

6H-SN




6H-OB




ITEM NO.	W	WEIGHT	ADDITIONAL DETAILS
6H-OB	33"x17"	3 lbs.	Oiled Bronze finish
6H-SN	33"x17"	3 lbs.	Satin Nickel finish

31142/6




14191/6




ROD KIT

When ordering, use rod kit item number only found below. Order single pendant separately.


ROD KIT-SN




ROD KIT-OB




ROD KIT-CHR

ITEM NO.	W	WEIGHT	ADDITIONAL DETAILS
ROD KIT-CHR	-	1 lb.	Polished Chrome finish, (1) 6" & (2) 12" extension rods, hang straight, & canopy
ROD KIT-OB	-	1 lb.	Oil Rubbed Bronze finish, (1) 6" & (2) 12" extension rods, hang straight, & canopy
ROD KIT-SN	-	1 lb.	Satin Nickel finish, (1) 6" & (2) 12" extension rods, hang straight, & canopy

6 LIGHT ROUND

When ordering pan only, use item number below. When ordering with pendants, use item number of single pendant + /6r (for 6 light round pan) + color code of glass (if applicable). See item numbers of 6 light pendants on this page as examples.



6R-SN
[Barcode]



6R-OB
[Barcode]



6R-CHR
[Barcode]

ITEM NO.	W	WEIGHT	ADDITIONAL DETAILS
6R-CHR	14"	3 lbs.	Polished Chrome finish
6R-OB	14"	3 lbs.	Oiled Bronze finish
6R-SN	14"	3 lbs.	Satin Nickel finish

8 LIGHT ROUND

When ordering pan only, use item number below. When ordering with pendants, use item number of single pendant + /8r (for 8 light round pan) + color code of glass (if applicable). See item numbers of 8 light pendants on this page as examples.



8R-SN
[Barcode]




8R-OB
[Barcode]



8R-CHR
[Barcode]

ITEM NO.	W	WEIGHT	ADDITIONAL DETAILS
8R-CHR	18"	4 lbs.	Polished Chrome finish
8R-OB	18"	4 lbs.	Oiled Bronze finish
8R-SN	18"	4 lbs.	Satin Nickel finish



544-6R-MO
[Barcode]



60044-6R
[Barcode]



31338/6R-VINW
[Barcode]



110-8R-BL
[Barcode]



46000/8R
[Barcode]



1477/8R-CAR
[Barcode]



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
31236/1	(1) 60W Med.	6"	11"	50"	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31791/1	(1) 60W Med.	7"	15"	62"	4 lbs.	Bulb #1102 optional
31792/1	(1) 60W Med.	9"	16"	63"	5 lbs.	Bulb #1102 optional
57030/1*	(1) 60W Med.	9"	13"	51"	4 lbs.	Polished Nickel finish
57040/1*	(1) 60W Med.	9"	13"	51"	4 lbs.	Gloss White Shade, Polished Nickel finish
57050/1*	(1) 60W Med.	9"	13"	51"	4 lbs.	Brushed Nickel finish
57060/1*	(1) 60W Med.	9"	13"	51"	4 lbs.	Oil Rubbed Bronze finish
57080/1*	(1) 60W Med.	9"	13"	51"	4 lbs.	Weathered Zinc Shade, Polished Nickel finish
66850/1*	(1) 100W Med.	8"	12"	52"	4 lbs.	Brushed Nickel finish
66860/1*	(1) 100W Med.	8"	12"	52"	4 lbs.	Oil Rubbed Bronze finish
66870/1*	(1) 100W Med.	8"	12"	52"	4 lbs.	Gloss White Shade, Polished Chrome finish
66892/1**	(1) 60W Med.	14"	14"	58"	3 lbs.	Bulb #1099 optional

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
66119-1*	(1) 100W Med.	8"	14"	88"	5 lbs.	Satin Nickel
66514-1*	(1) 100W Med.	8"	14"	46"	5 lbs.	Polished Nickel finish, Gloss White shade
66524-1*	(1) 100W Med.	8"	14"	46"	5 lbs.	Satin Nickel finish, Gloss White shade
67712-1*	(1) 100W Med.	8"	14"	46"	5 lbs.	Bulb #1092 optional, Antique Copper finish
67722-1*	(1) 100W Med.	8"	14"	46"	5 lbs.	Bulb #1092 optional, Oiled Bronze finish
67732-1*	(1) 100W Med.	8"	14"	46"	5 lbs.	Bulb #1092 optional, Polished Nickel finish
67742-1*	(1) 100W Med.	8"	14"	46"	5 lbs.	Bulb #1092 optional, Satin Nickel finish
66851/1	(1) 100W Med.	8"	12"	39-71"	5 lbs.	Brushed Nickel finish
66861/1	(1) 100W Med.	8"	12"	39-71"	5 lbs.	Oil Rubbed Bronze finish
66871/1	(1) 100W Med.	8"	12"	39-71"	5 lbs.	Gloss White Shade, Polished Chrome finish
66880/1**	(1) 100W Med.	8"	12"	52"	4 lbs.	Weathered Zinc shade, Polished Nickel finish
66881/1	(1) 100W Med.	8"	12"	39-71"	5 lbs.	Weathered Zinc shade, Polished Nickel finish

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
 ** (1) 6", (1) 12" & (1) 24" extension rods w/hang straight included

* 1-6" and 2-12" extension rods with hang straight included
 ** (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
66112-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Polished Nickel with White Glass
66122-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Satin Nickel with White Glass
66132-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Oiled Bronze with Amber Glass
66139-1*	(1) 100W Med.	8"	14"	88"	5 lbs.	Oiled Bronze
66142-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Antique Copper with White Glass
66149-1*	(1) 100W Med.	8"	14"	88"	5 lbs.	Antique Copper
66159-1*	(1) 100W Med.	8"	14"	88"	5 lbs.	Polished Nickel
66412-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Polished Nickel with Cappa Shells
66632-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Oiled Bronze finish with White Glass
66751-1*	(1) 100W Med.	7"	16"	90"	6 lbs.	Bulb #1092 optional
66761-1*	(1) 100W Med.	7"	16"	90"	6 lbs.	Bulb #1092 optional
66771-1*	(1) 100W Med.	7"	16"	90"	6 lbs.	Bulb #1092 optional
66781-1*	(1) 100W Med.	7"	16"	90"	6 lbs.	Bulb #1092 optional

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
31510/1	(1) 60W Med.	6"	13"	52"	4 lbs.	Bulb #1092 optional
55011/1	(1) 100W Med.	11"	7"	81"	2 lbs.	Polished Nickel finish, Bulb #1092 optional
55021/1	(1) 100W Med.	11"	7"	81"	2 lbs.	Brushed Nickel finish, Bulb #1092 optional
55031/1	(1) 100W Med.	11"	7"	81"	2 lbs.	Antique Copper finish, Bulb #1092 optional
55041/1	(1) 100W Med.	11"	7"	81"	2 lbs.	Oil Rubbed Bronze finish, Bulb #1092 optional
66151-1*	(1) 100W Med.	5"	11"	88"	4 lbs.	Polished Chrome with White Glass
66161-1*	(1) 100W Med.	5"	11"	88"	4 lbs.	Satin Nickel with White Glass
66171-1*	(1) 100W Med.	5"	11"	88"	4 lbs.	Oiled Bronze with Amber Glass
66181-1*	(1) 100W Med.	5"	11"	88"	4 lbs.	Antique Copper with White Glass
66422-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Satin Nickel with Cappa Shells
66432-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Oiled Bronze with Cappa Shells
66442-1*	(1) 100W Med.	6"	17"	90"	6 lbs.	Antique Copper with Cappa Shells
66671-1*	(1) 100W Med.	5"	11"	43"	4 lbs.	Oiled Bronze finish with White Glass

* 1-6" and 2-12" extension rods with hang straight included

* 1-6" and 2-12" extension rods with hang straight included



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
010-AC	(1) 60W Med. Torpedo	7"	9"	83"	2 lbs.	Antique Copper, Includes 6 feet of Cord
31423/1	(1) 60W Med.	6"	8"	54"	4 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
31482/1	(1) 60W Med.	6"	8"	88"	3 lbs.	Bulb #1092 optional
63012-1	(1) 60W Med.	4"	26"	64"	3 lbs.	Includes 3 ft. of chain
63053-1	(1) 60W Med.	4"	26"	68"	3 lbs.	Bulb #1092 optional
65049-1	(1) 60W Med.	12"	13"	-	5 lbs.	Bellwether Copper
65060-1	(1) 100W Med.	8"	39-71"	71"	6 lbs.	Bellwether Copper
65070-1	(1) 100W Med.	8"	39-71"	71"	6 lbs.	Oiled Bronze
65080-1	(1) 100W Med.	8"	39-71"	71"	6 lbs.	Aged Pewter
65090-1	(1) 100W Med.	7"	39-70"	70"	5 lbs.	Oiled Bronze with White Glass
66316/1	(1) 60W Med.	4"	11"	85"	2 lbs.	Includes 6 feet of brown cord, Polished Chrome finish
66326/1	(1) 60W Med.	4"	11"	85"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
17208/1	(1) 75W Med.	7"	10"	84"	2 lbs.	Oil Rubbed Bronze finish
17231/1*	(1) 60W Med.	10"	10"	47"	5 lbs.	Polished Chrome finish
17241/1*	(1) 60W Med.	10"	10"	47"	5 lbs.	Brushed Nickel finish
17251/1*	(1) 60W Med.	10"	10"	47"	5 lbs.	Oil Rubbed Bronze finish
55001/1	(1) 100W Med.	6"	10"	54"	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
60005-1**	(1) 100W Med.	6"	10"	42"	4 lbs.	Polished Chrome finish
60015-1**	(1) 100W Med.	6"	10"	42"	4 lbs.	Aged Bronze finish
66315/1	(1) 60W Med.	4"	11"	85"	2 lbs.	Includes 6 feet of brown cord, Polished Chrome finish
66317/1	(1) 60W Med.	4"	11"	86"	2 lbs.	Includes 6 feet of brown cord, Polished Chrome finish
66325/1	(1) 60W Med.	4"	11"	85"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
67040/1	(1) 60W Med.	10"	6"	80"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze finish
67042/1	(1) 60W Med.	10"	6"	80"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze/Chrome finish

* (1) 6", (1) 12" & (1) 18" extension rods w/hang straight included ** 1-6" and 2-12" extension rods with hang straight included



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
14191/1	(1) 60W Med.	7"	11"	83"	2 lbs.	Bulb #1092 optional
14192/1	(1) 60W Med.	11"	15"	67"	3 lbs.	Bulb #1092 optional
14240/1	(1) 60W Med.	10"	7"	45"	2 lbs.	Includes 6 ft. of cord
66817-1	(1) 60W Med.	9"	10"	83"	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
66818-1	(1) 100W Med.	7"	10"	83"	3lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
66827-1	(1) 60W Med.	9"	10"	83"	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
66828-1	(1) 100W Med.	7"	10"	83"	3 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
66833-1	(1) 60W Med.	9"	43-74"	-	6 lbs.	Bulb #1092 optional
66843-1	(1) 60W Med.	9"	43-74"	-	6 lbs.	Bulb #1092 optional
67041/1	(1) 60W Med.	10"	6"	80"	2 lbs.	Includes 6 feet of brown cord, Oil Rubbed Bronze/White finish
67051/1	(1) 60W Med.	10"	6"	80"	2 lbs.	Includes 6 feet of clear cord, Polished Chrome/White finish
67063/1	(1) 60W Med.	5"	14"	51"	4 lbs.	Bulb #1102 optional

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
14241/1	(1) 60W Med.	10"	12"	50"	3 lbs.	Bulb #1092 optional
14242/1	(1) 60W Med.	9"	14"	52"	3 lbs.	Bulb #1092 optional
17054/1	(1) 60W Med.	8"	7"	81"	3 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
46220/1	(1) 100W Med.	6"	16"	54"	3 lbs.	Bulb #1099 optional
46221/1	(1) 100W Med.	9"	15"	53"	4 lbs.	Bulb #1092 optional
46222/1	(1) 100W Med.	10"	14"	52"	4 lbs.	Bulb #1092 optional
63024-1	(1) 100W Med.	7"	12"	86"	3 lbs.	Bulb #1092 optional
63025-1	(1) 100W Med.	6"	12"	86"	3 lbs.	Bulb #1092 optional
63034-1	(1) 100W Med.	7"	12"	86"	3 lbs.	Bulb #1092 optional
63035-1	(1) 100W Med.	6"	12"	86"	3 lbs.	Bulb #1092 optional
66216-1	(1) 60W Med.	5"	25"	83"	2 lbs.	Includes 3 ft. of chain
69029-1*	(1) 75W Med.	8"	12"	44"	3 lbs.	Satin Nickel

* 1-6" and 2-12" extension rods with hang straight included



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
14285/1*	(1) 60W Med.	2"	9"	41"	3 lbs.	Bulb #1092 optional
14290/1	(1) 60W Med.	8"	12"	50"	3 lbs.	
14300/1	(1) 60W Med.	10"	8"	82"	3 lbs.	
14306/1	(1) 60W Med.	7"	13"	87"	3 lbs.	Bulb #1092 optional
14310/1	(1) 40W Cand.	4"	9"	83"	2 lbs.	
14311/1	(1) 60W Med.	7"	11"	85"	5 lbs.	
66194-1	(1) 60W Med.	8"	8"	81"	3 lbs.	1-6" and 2-12" extension rods with hang straight included
69039-1*	(1) 75W Med.	8"	12"	44"	3 lbs.	Oiled Bronze
69042-1*	(1) 75W Med.	8"	8"	40"	3 lbs.	Satin Nickel
69043-1*	(1) 75W Med.	9"	14"	46"	3 lbs.	Satin Nickel
69052-1*	(1) 75W Med.	8"	8"	40"	3 lbs.	Oiled Bronze
69053-1*	(1) 75W Med.	9"	14"	46"	3 lbs.	Oiled Bronze

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
2426/1	(1) 60W Med.	6"	16"	90"	3 lbs.	
5972/1	(1) 60W Cand.	5"	8"	82"	3 lbs.	(1) 6" & (2) 12" extension rods with hang straight included
11001/1	(1) 60W Cand.	6"	22"	96"	5 lbs.	(1) 6" & (2) 12" extension rods with hang straight included
11285/1	(1) 60W Cand.	6"	9"	83"	4 lbs.	(1) 6" & (2) 12" extension rods with hang straight included
11554/1	(1) 60W Cand.	11"	18"	58"	4 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
11705/1	(1) 100W Med.	10"	16"	54"	4 lbs.	Aged Silver finish
11706/1	(1) 100W Med.	10"	16"	54"	4 lbs.	Spanish Bronze finish
14004/1 + 1	(1) 60W Cand. (1) 50W GU10	10"	23"	96"	4 lbs.	(1) 6" & (2) 12" extension rods with hang straight included
15976/1	(1) 60W Cand.	6"	9"	83"	2 lbs.	Aged Silver finish
15986/1	(1) 60W Cand.	6"	9"	83"	2 lbs.	Dark Bronze finish
16242/1	(1) 100W Med.	6"	9"	48"	4 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31772/1	(1) 60W Med.	8"	8"	46"	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included

*1-6" and 2-12" extension rods with hang straight included



18133/1

18123/1

18141/1

12017/1



12008/1

12002/1

11685/1

10480/1



66460/1

251-BK

9325/1

369-VA

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
251-BK	(1) 75W Med.	10"	25"	75"	7 lbs.	48" Chain
369-VA	(1) 75W Med.	10"	25"	75"	10 lbs.	48" Chain
9325/1	(1) 60W Med.	6"	19"	57"	3 lbs.	
10480/1	(1) 60W Med.	7"	8"	46"	2 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
11685/1	(1) 100W Med.	5"	9"	48"	4 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
12002/1	(1) 100W Med.	10"	17"	55"	5 lbs.	Rust finish
12008/1	(1) 60W Cand.	10"	16"	56"	4 lbs.	Antique White finish
12017/1	(1) 60W Med.	10"	15"	53"	3 lbs.	Antique White finish
18123/1	(1) 100W Med.	10"	10"	48"	3 lbs.	Antique White finish
18133/1	(1) 100W Med.	10"	10"	48"	3 lbs.	Deep Rust finish
18141/1	(1) 100W Med.	8"	9"	49"	2 lbs.	Bulb #1092 optional
66460/1	(1) 60W Med.	13"	11"	51"	5 lbs.	Bulb #1092 optional



078-TB-01

078-TB-03

078-TB-04

078-TB-07

078-TB-09

078-TB-10

078-TB-12

078-TB-13

078-TB-17

078-TB-19

078-TB-21

078-TB-28

Tiffany Bronze Finish
 Size: W: 6" H: 24"
 Max Height: 62"
 18" Stem 36" Chain
 Lamp: (1) 75W Med.
 Weight: 5 lbs.

MIX - N - MATCH SHADES

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

LED Option LED option available. When ordering include -LED after item number.



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
08018-TBH	(1) 75W Med.	7"	27"	65"	5 lbs.	18" Stem 36" Chain
629-AB	(1) 75W Med.	7"	39"	77"	6 lbs.	18" Stem 36" Chain
648-BC	(1) 75W Med.	8"	30"	68"	6 lbs.	18" Stem 36" Chain
15033/1	(1) 60W Med.	6"	19"	92"	3 lbs.	(1) 6" & (2) 12" extension rods with hang straight included
31032/1	(1) 60W Med.	7"	8"	40"	3 lbs.	(1) 6" & (2) 12" extension rods with hang straight included
46020/1	(1) 60W Med.	6"	10"	54"	2 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
60018-1	(1) 100W Med.	5"	8"	81"	3 lbs.	Includes 6 Feet of Cord
70000-1CW	(1) 75W Med.	5"	12"	86"	2 lbs.	Comet White glass, Includes 6 Feet of Cord
70000-1HB	(1) 75W Med.	5"	12"	86"	2 lbs.	Hazy Beige glass, Includes 6 Feet of Cord
70000-1IR	(1) 75W Med.	5"	12"	86"	2 lbs.	Inferno Red glass, Includes 6 Feet of Cord
70066-1	(1) 60W Med.	6"	9"	83"	2 lbs.	Includes 6 feet of cord
72001-1	(1) 60W Med.	7"	10"	83"	3 lbs.	Includes 6 Feet of Cord

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
7634/1	(1) 60W Med.	7"	15"	88"	2 lbs.	G16 1/2 bulbs recommended
7644/1	(1) 60W Med.	7"	15"	88"	2 lbs.	G16 1/2 bulbs recommended
11762/1	(1) 60W G9 (included)	6"	12"	51"	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
14121/1	(1) 100W Med.	7"	8"	52"	4 lbs.	(1) 6" & (3) 12" extension rods w/hang straight included
14201/1	(1) 60W Med.	10"	11"	43"	6 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
17644/1	(1) 60W Med.	7"	15"	89"	2 lbs.	G16 1/2 bulbs recommended
22025/1	(1) 60W Med.	8"	15"	54"	5 lbs.	
31123/1	(1) 60W Med.	6"	11"	49"	4 lbs.	
31185/1	(1) 60W Med.	8"	9"	83"	2 lbs.	Bulb #1092 optional
31333/1	(1) 75W Med.	7"	23"	61"	3 lbs.	(1) 6", (1) 12" & (1) 18" extension rods w/hang straight included
31302/1	(1) 75W Med.	8"	18"	92"	2 lbs.	Polished Nickel finish
31312/1	(1) 75W Med.	8"	18"	92"	2 lbs.	Mocha finish
57026/1	(1) 100W Med.	6"	8"	52"	3 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.



73011-1



73021-1



73041-1



73031-1



72021-1



31340/1SN
Satin Nickel



31340/1OB
Oiled Bronze



31340/1MO
Medium Oak



70046-1



31554/1



Bulb #1092 optional



72072-1



72062-1



31340/1BW
Burl Wood



31340/1DW
Dark Walnut



10073/1



1474/1




46200/1



46203/1



46210/1



46213/1



1474/1MAR



1474/1CAR



1474/1JAS



1474/1CRW



ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
31554/1	(1) 60W Med.	7"	16"	61"	3 lbs.	(1) 6", (1) 12" & (1) 24" extension rods w/hang straight included
46200/1	(1) 60W Med.	5"	9"	82"	2 lbs.	Includes 6 feet of clear cord
46203/1	(1) 100W Med.	8"	18"	92"	3 lbs.	Includes 6 feet of clear cord
46210/1	(1) 60W Med.	5"	9"	82"	2 lbs.	Includes 6 feet of clear cord
46213/1	(1) 100W Med.	8"	18"	92"	3 lbs.	Includes 6 feet of clear cord
70046-1	(1) 60W Med.	6"	9"	83"	3 lbs.	Includes 6 feet of cord
72062-1	(1) 60W Med.	6"	9"	41"	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
72072-1	(1) 60W Med.	6"	9"	41"	4 lbs.	(1) 6" & (2) 12" extension rods w/hang straight included
73011-1	(1) 60W Med.	5"	8"	81"	2 lbs.	Includes 6 feet of clear cord
73021-1	(1) 60W Med.	5"	8"	81"	2 lbs.	Includes 6 feet of clear cord
73031-1	(1) 60W Med.	5"	8"	81"	2 lbs.	Includes 6 feet of clear cord
73041-1	(1) 60W Med.	5"	8"	81"	2 lbs.	Includes 6 feet of clear cord

ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
1474/1	(1) 40W G9 (included)	7"	9"	83"	2 lbs.	(1) 6" and (2) 12" extension rods with hang straight included
1474/1CAR	(1) 40W G9 (included)	7"	9"	83"	2 lbs.	Polished Chrome finish, Caribbean glass
1474/1CRW	(1) 40W G9 (included)	7"	9"	83"	2 lbs.	Polished Chrome finish, Creme White glass
1474/1JAS	(1) 40W G9 (included)	7"	9"	83"	2 lbs.	Polished Chrome finish, Jasper glass
1474/1MAR	(1) 40W G9 (included)	7"	9"	83"	2 lbs.	Polished Chrome finish, Mars glass
10073/1	(1) 60W Med.	6"	8"	82"	2 lbs.	Includes 6 feet of clear cord, Satin Nickel finish
31340/1BW	(1) 50W GU10 (included)	4"	10"	86"	1 lb.	Includes 6 feet of clear cord
31340/1DW	(1) 50W GU10 (included)	4"	10"	86"	1 lb.	Includes 6 feet of clear cord
31340/1MO	(1) 50W GU10 (included)	4"	10"	86"	1 lb.	Includes 6 feet of clear cord
31340/1OB	(1) 50W GU10 (included)	4"	10"	86"	1 lb.	Includes 6 feet of clear cord
31340/1SN	(1) 50W GU10 (included)	4"	10"	86"	1 lb.	Includes 6 feet of clear cord
72021-1	(1) 60W Med.	7"	11"	86"	4 lbs.	Includes 6 Feet of Cord




ITEM NO.	BULB	W	H	MAX. H	WEIGHT	ADDITIONAL DETAILS
5123/1	(1) 60W Med.	10"	11"	85"	2 lbs.	White finish, includes 6 feet of clear cord
5137/1	(1) 60W Cand.	8"	9"	83"	3 lbs.	Satin Nickel finish, includes 6 feet of clear cord
2997/1A	(1) 60W Cand.	4"	6"	80"	2 lbs.	Includes 6 feet of clear cord
10172/1	(1) 60W Med.	8"	8"	40"	4 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
19031/1	(1) 60W Med.	6"	7"	81"	2 lbs.	White Sawgrass, Includes 6 feet of clear cord
19061/1	(1) 60W Med.	6"	7"	81"	2 lbs.	Bamboo Stems, Includes 6 feet of clear cord
31037/1	(1) 60W Med.	8"	13"	87"	2 lbs.	Includes 6 feet of clear cord
31041/1	(1) 60W Med.	8"	13"	87"	2 lbs.	Includes 6 feet of clear cord
31045/1	(1) 60W Med.	8"	13"	87"	2 lbs.	Includes 6 feet of cord
31073/1	(1) 60W Med.	8"	13"	87"	2 lbs.	Includes 6 feet of cord
31102/1	(1) 100W Med.	10"	6"	38"	4 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
31103/1	(1) 100W Med.	8"	9"	41"	5 lbs.	(1) 6" & (2) 12" extension rods w/ hang straight included
53000/1	(1) 60W Med.	7"	8"	82"	1 lb.	Includes 6 feet of clear cord



Adapter screws into a medium base recessed socket, making it ready to install a light fixture (up to 5 lbs.) in less than five minutes.

- No assembly required
- No need for an electrician
- No costly & messy construction
- No painting or finish work
- Best of all, NO HASSLE

It's as simple as 1,2,3



before



after

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
LA100	-	8"	-	-	1 lb.	White finish

RECESSED LIGHTING CONVERSION KIT



SWINGARMS



31477/1



31332/1



66825-1



66815-1



63060-1



63050-1



66826-1



66816-1

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
31332/1	(1) 100W Med.	10"	16"	27"	4 lbs.	Comes w/cord cover that can be removed for direct wiring into junction box. Polished Nickel finish
31477/1	(1) 100W Med.	12"	20"	12-25"	3 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Polished Nickel finish
63050-1	(1) 100W Med.	11"	15"	12-26"	4 lbs.	Shade included, Comes w/cord cover and plug that can be removed for direct wiring into junction box. Silvered Graphite finish
63060-1	(1) 100W Med.	11"	15"	12-26"	4 lbs.	Shade included, Comes w/cord cover and plug that can be removed for direct wiring into junction box. Aged Bronze finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66815-1	(1) 100W Med.	7"	18"	33"	5 lbs.	Comes w/cord cover that can be removed for direct wiring into junction box. Weathered Zinc finish
66816-1	(1) 60W Med.	9"	18"	34"	5 lbs.	Comes w/cord cover that can be removed for direct wiring into junction box. Oiled Bronze finish
66825-1	(1) 100W Med.	7"	18"	33"	5 lbs.	Comes w/cord cover that can be removed for direct wiring into junction box. Oiled Bronze finish
66826-1	(1) 60W Med.	9"	18"	34"	5 lbs.	Comes w/cord cover that can be removed for direct wiring into junction box. Weathered Zinc finish



11210/1



11220/1



31530/1



31520/1



17047/1



17016/1



17026/1



17027/1

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11210/1	(1) 3-Way 150W Med.	12"	15"	12-25"	3 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Polished Chrome finish
11220/1	(1) 3-Way 150W Med.	12"	15"	12-25"	3 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Antique Brass finish
31520/1	(1) 100W Med.	11"	16"	12-25"	4 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Brushed Antique Brass finish
31530/1	(1) 100W Med.	11"	16"	12-25"	4 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Brushed Nickel finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17016/1	(1) 3-Way 150W Med.	12"	17"	24"	2 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Satin Nickel finish
17026/1	(1) 3-Way 150W Med.	12"	17"	24"	2 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Aged Bronze finish
17027/1	(1) 3-Way 150W Med.	14"	56"	22"	11 lbs.	Aged Bronze finish
17047/1	(1) 3-Way 150W Med.	14"	56"	22"	11 lbs.	Satin Nickel finish



10109/1



10108/1



10293/1



10292/1



10260/1



10160/1



10291/1



10106/1

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10108/1	(1) 3-Way 150W Med.	12"	16"	12-22"	3 lbs.	Polished Chrome finish
10109/1	(1) 3-Way 150W Med.	14-21"	64"	-	16 lbs.	Polished Chrome finish
10292/1	(1) 3-Way 150W Med.	12"	16"	12-22"	3 lbs.	Aged Bronze finish
10293/1	(1) 3-Way 150W Med.	14-21"	64"	-	16 lbs.	Aged Bronze finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10106/1	(1) 3-Way 150W Med.	11"	13"	12-25"	3 lbs.	Polished Chrome finish
10160/1	(1) 60W Med.	10"	14"	10-26"	4 lbs.	Polished Nickel finish
10260/1	(1) 60W Med.	10"	14"	10-26"	4 lbs.	Brushed Antique Brass finish
10291/1	(1) 3-Way 150W Med.	11"	13"	12-25"	3 lbs.	Aged Bronze finish



17150/1



31540/1



17153/1



31048/1



31069/1



10112/1



54018/1

LED

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17150/1	(1) 75W Med.	7"	13"	15-20"	2 lbs.	Brushed Nickel finish
17153/1	(1) 75W Med.	9"	12"	11-16"	2 lbs.	Brushed Nickel finish
31540/1	(1) 100W Med.	11"	16"	12-24"	4 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Polished Nickel finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10112/1	(1) 40W G9 (included)	7"	11"	9-22"	3 lbs.	Satin Nickel finish
31048/1	(1) 100W Med.	10"	15"	11-24"	3 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Aged Bronze finish
31069/1	(1) 100W Med.	10"	15"	11-24"	3 lbs.	Comes w/cord cover and plug that can be removed for direct wiring into junction box. Aged Bronze finish
54018/1	(1) 5W-450 Lumen LED (integrated)	5"	5"	16-28"	3 lbs.	3000K, 80 CRI, Brushed Nickel finish



079-TB-01



079-TB-03



079-TB-04



079-TB-07



079-TB-09



079-TB-10



079-TB-12



079-TB-13



079-TB-17



079-TB-19



079-TB-21



079-TB-28



Swingarm Sconce
Tiffany Bronze Finish
Size: W: 7" H: 12" Ext: 24"

Lamp: (1) 75W Med.
Weight: 5 lbs.

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

MIX - N - MATCH SHADES



10151/1PC-*
Shown in Fire Red



10151/1PC-*
Shown in Snow White



10151/1PC-*
Shown in Espresso




10151/1DR-*
Shown in Fire Red



10151/1DR-*
Shown in Snow White



10151/1DR-*
Shown in Espresso



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10151/1PC-*	(1) 100W Med.	22"	10"	10-22"	3 lbs.	Polished Chrome finish
10151/1DR-*	(1) 100W Med.	22"	10"	10-22"	3 lbs.	Dark Rust finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* Item numbers shown are for frame. Please include glass color code after item #.



POCKET SCONCES



31505/1



66280-2



31480/1



46040/2



11284/2



11584/1



31420/1



31210/1




63020-1



5970/2




6238/2



16241/2



31095/1



31770/2



11780/2



12023/2



2400/2



2490/1




ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
11780/2	(2) 60W Cand.	14"	10"	7"	4 lbs.	Pocket Sconce
31095/1	(1) 60W Cand.	8"	9"	4"	2 lbs.	ADA Compliant
31210/1	(1) 60W Med.	7"	12"	4"	5 lbs.	ADA Compliant, Bulb #1092 optional
31420/1	(1) 60W Med.	8"	10"	4"	3 lbs.	ADA compliant
31480/1	(1) 60W Med.	8"	10"	4"	4 lbs.	Bulb #1092 optional, Pocket Sconce, ADA compliant
31505/1	(1) 60W Med.	10"	15"	5"	5 lbs.	Bulb #1092 Optional
31770/2	(2) 60W Cand.	15"	8"	8"	4 lbs.	Pocket Sconce
63020-1	(1) 60W Med.	7"	12"	4"	5 lbs.	ADA Compliant, Bulb #1092 optional
66280-2	(2) 60W Cand.	11"	13"	6"	6 lbs.	Pocket Sconce

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
2400/2	(2) 60W Cand.	14"	8"	6"	7 lbs.	Pocket Sconce
2490/1	(1) 60W Cand.	7"	11"	5"	4 lbs.	Pocket Sconce
5970/2	(2) 60W Cand.	13"	7"	6"	4 lbs.	Pocket Sconce
6238/2	(2) 60W Cand.	14"	6"	6"	5 lbs.	Pocket Sconce
11284/2	(2) 60W Cand.	11"	11"	6"	4 lbs.	Pocket Sconce
11584/1	(1) 60W Cand.	6"	9"	4"	3 lbs.	ADA Compliant
12023/2	(2) 60W Cand.	14"	8"	8"	7 lbs.	Pocket Sconce
16241/2	(2) 60W Cand.	11"	8"	5"	3 lbs.	Pocket Sconce
46040/2	(2) 60W Cand.	12"	18"	5"	4 lbs.	Pocket Sconce



18130/2



70098-2




08028-CB



10280/2



10270/2



1520/1



08032-BC



08030-AB




72077-1



1510/1



31455/1



31465/1



70064-2



11237/1




14050/1



22000/2



31450/1



31460/1



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08028-CB	(2) 60W Med.	14"	8"	4"	2 lbs.	Pocket Sconce ADA Compliant
08030-AB	(2) 60W Med.	14"	8"	4"	2 lbs.	Pocket Sconce ADA Compliant
08032-BC	(2) 60W Med.	14"	7"	4"	2 lbs.	Pocket Sconce ADA Complaint
11237/1	(1) 60W Cand.	10"	10"	5"	2 lbs.	Pocket Sconce
14050/1	(1) 60W Med.	14"	16"	9"	7 lbs.	Pocket Sconce
18130/2	(2) 60W Cand.	12"	9"	7"	3 lbs.	Pocket Sconce
70064-2	(2) 60W Med.	10"	6"	5"	2 lbs.	Pocket Sconce
70098-2	(2) 60W Med.	16"	8"	8"	3 lbs.	Pocket Sconce
72077-1	(1) 60W Med.	13"	6"	7"	3 lbs.	Pocket Sconce

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
1510/1	(1) 60W Med.	8"	16"	5"	4 lbs.	Pocket Sconce
1520/1	(1) 60W Med.	8"	16"	5"	4 lbs.	Pocket Sconce
10270/2	(2) 40W G9 (included)	7"	14"	3"	4 lbs.	Pocket Sconce, ADA Compliant
10280/2	(2) 40W G9 (included)	7"	14"	3"	4 lbs.	Pocket Sconce, ADA Compliant
22000/2	(2) 60W Cand.	12"	7"	7"	3 lbs.	Pocket Sconce
31450/1	(1) 60W Cand.	6"	14"	5"	4 lbs.	Oil Rubbed Bronze finish
31455/1	(1) 60W Cand.	7"	18"	4"	2 lbs.	Polished Nickel finish, ADA compliant
31460/1	(1) 60W Cand.	6"	14"	5"	4 lbs.	Polished Nickel finish
31465/1	(1) 60W Cand.	7"	18"	4"	2 lbs.	Antique Gold Leaf finish, ADA compliant




14200/1



72000-2



70044-2




9003/2




8884/2



8894/2



10380/1



10370/1



10371/1



66940/1



66930/1



66950/1



73020-2



73030-2



60016-2



66920/2



72070-2



72060-2

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10370/1	(1) 60W Med.	12"	6"	3"	3 lbs.	Pocket Sconce, ADA Compliant
10371/1	(1) 60W Med.	12"	6"	3"	3 lbs.	Pocket Sconce, ADA Compliant
10380/1	(1) 60W Med.	12"	6"	3"	2 lbs.	Pocket Sconce, ADA Compliant
14200/1	(1) 60W Cand.	10"	16"	6"	7 lbs.	Bulb #1101 optional
60016-2	(2) 60W Cand.	6"	14"	4"	4 lbs.	Sconce ADA Compliant
70044-2	(2) 60W Cand.	9"	12"	5"	3 lbs.	Pocket Sconce
72000-2	(2) 60W Cand.	10"	6"	5"	3 lbs.	Pocket Sconce
73020-2	(2) 60W Cand.	7"	15"	3"	3 lbs.	Sconce ADA Compliant
73030-2	(2) 60W Cand.	7"	15"	3"	3 lbs.	Sconce ADA Compliant

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
8884/2	(2) 60W Cand.	12"	6"	6"	5 lbs.	Pocket sconce
8894/2	(2) 60W Cand.	12"	6"	6"	5 lbs.	Pocket sconce
9003/2	(2) 60W Cand.	17"	10"	6"	6 lbs.	Pocket sconce
66920/2	(2) 60W Cand.	14"	14"	7"	3 lbs.	
66930/1	(1) 60W Cand.	8"	11"	5"	2 lbs.	
66940/1	(1) 60W Cand.	8"	11"	5"	2 lbs.	
66950/1	(1) 60W Cand.	7"	9"	4"	2 lbs.	ADA Compliant
72060-2	(2) 60W Cand.	7"	10"	5"	3 lbs.	
72070-2	(2) 60W Cand.	7"	10"	5"	3 lbs.	



14120/1



53002/1



19030/2



31030/1



31100/2



19060/2



31035/2



31040/2



31021/1



31020/2




31044/2




31070/2




10360/1



10088/1



426-1M



426-1WS



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10360/1	(1) 60W Med.	6"	8"	4"	2 lbs.	ADA Compliant
14120/1	(1) 60W Med.	7"	12"	6"	3 lbs.	
19030/2	(2) 60W Med.	7"	11"	4"	3 lbs.	White Sawgrass, ADA Compliant
19060/2	(2) 60W Med.	7"	11"	4"	3 lbs.	Bamboo Stems, ADA Compliant
31035/2	(2) 60W Cand.	11"	8"	5"	2 lbs.	Pocket Sconce
31040/2	(2) 60W Cand.	11"	8"	5"	2 lbs.	Pocket Sconce
31044/2	(2) 60W Cand.	11"	8"	5"	2 lbs.	Pocket Sconce
31070/2	(2) 60W Cand.	11"	8"	5"	2 lbs.	Pocket Sconce
53002/1	(1) 60W Cand.	9"	8"	5"	1 lb.	Pocket Sconce

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
426-1M	(1) 60W Med.	8"	10"	4"	2 lbs.	Multi glass, ADA Compliant
426-1WS	(1) 60W Med.	8"	10"	4"	2 lbs.	White Swirl glass, ADA Compliant
10088/1	(1) 60W Cand.	6"	8"	3"	2 lbs.	ADA Compliant
31020/2	(2) 60W Cand.	12"	6"	5"	4 lbs.	Pocket Sconce
31021/1	(1) 60W Med.	10"	5"	4"	2 lbs.	Pocket Sconce, ADA Compliant
31030/1	(1) 60W Cand.	10"	10"	4"	3 lbs.	Pocket Sconce, ADA Compliant
31100/2	(2) 60W Cand.	10"	6"	4"	2 lbs.	Pocket Sconce, ADA Compliant



17154/2



LED

Reading Light



17155/2



LED

Reading Light



17151/2



LED

Reading Light



17160/1



17156/1



17161/2



17152/1



SCONCES

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
17151/2	(1) 75W Med. (1) 3W-120 Lumen LED	7"	19"	9"	2 lbs.	Brushed Nickel finish, 3000K
17152/1	(1) 75W Med.	6"	10"	9"	1 lb.	Brushed Nickel finish
17154/2	(1) 75W Med. (1) 3W-120 Lumen LED	11"	15"	8"	1 lb.	Brushed Nickel finish, 3000K
17155/2	(1) 75W Med. (1) 3W-120 Lumen LED	7"	19"	8"	1 lb.	Brushed Nickel finish, 3000K
17156/1	(1) 75W Med.	8"	11"	8"	1 lb.	Brushed Nickel finish
17160/1	(1) 75W Med.	7"	10"	9"	1 lb.	Brushed Nickel finish
17161/2	(2) 75W Med.	14"	10"	9"	2 lbs.	Brushed Nickel finish



46030/1



61040-1



66250-1+1



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
46030/1	(1) 60W Med.	8"	23"	5"	1 lb.	Silver Leaf finish, textured white linen shade
61040-1	(1) 60W Cand.	5"	14"	6"	1 lb.	Oiled Bronze finish, white fabric shade
66250-1+1	(1) 60W Cand. (1) 20W MR16	5"	12"	5"	4 lbs.	Oiled Bronze finish, opal etched glass



10150/1PC-*
Shown in Fire Red



10150/1PC-*
Shown in Snow White



10150/1PC-*
Shown in Espresso



10150/1DR-*
Shown in Fire Red



10150/1DR-*
Shown in Snow White



10150/1DR-*
Shown in Espresso



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
10150/1PC-*	(1) 60W Med.	6"	9"	7"	2 lbs.	Polished Chrome finish
10150/1DR-*	(1) 60W Med.	6"	9"	7"	2 lbs.	Dark Rust finish

Due to its hand-made nature, each piece of blown glass will vary slightly in color and pattern.

* Item numbers shown are for frame. Please include glass color code after item #

Fixtures shown with Fire Red, Snow White, and Espresso glass as examples. This collection is also available with glass colors shown.

SCONCES

CELINA

This collection showcases blown glass with a simple, yet elegant frame finished in Polished Chrome and Dark Rust. Choose from various glass options to complement your décor.



55005/6



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
55005/6	(6) 60W Cand.	19"	65"	9"	13 lbs.	Shades included



26004/1



Draping Leaf Wall Sconce



26000/2



Double Torch Wall Sconce



26001/1



Mirrored Candlestick Wall Sconce

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
26000/2	(2) 60W Cand.	8"	29"	6"	5 lbs.	On/Off switch, Comes w/cord cover and plug that can be removed for direct wiring into junction box.
26001/1	(1) 60W Cand.	6"	32"	4"	6 lbs.	ADA Compliant, On/Off switch, Comes w/cord cover and plug that can be removed for direct wiring into junction box.
26004/1	(1) 60W Cand.	8"	29"	6"	4 lbs.	On/Off switch, Comes w/cord cover and plug that can be removed for direct wiring into junction box.

SPRIG

Inspired by a wall climbing vine, the sprig series blends complimentary elements into a stunning wall art sculpture or dining room fixture. Offsetting thick branches provide a realistic appearance, while a hand applied Silver Leaf finish and cream fabric shades add flair for a more modern designer statement.

TORCH SCONCES

These dramatic torchiere style wall sconces cast a warm, inviting light. Each sconce has a highly detailed frame with a rich, multi-layered finish and a unique shade that compliments the design.



GAME ROOM

Island and Billiard

TIFFANY LIGHTING

The stained glass Billiard Collection takes its cues from the game, sporting colorful, detailed illustrations and classic Victorian themes. Use over a pool table or kitchen island for optimal illumination.



70053-4
[Barcode]



70083-4
[Barcode]



08030-AB
[Barcode]

70113-4
[Barcode]



361-VA
[Barcode]

70023-4
[Barcode]



348-VA
[Barcode]




70064-2
[Barcode]

70061-3
[Barcode]



190-11-TB-T8
[Barcode]



770-3-MB-A
[Barcode]



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
08030-AB	(2) 60W Med.	14"	8"	4"	2 lbs.	Tiffany Bronze Pocket Sconce ADA Compliant
190-11-TB-T8	(3) 100W Med.	58"	16"	14"	29 lbs.	Tiffany Bronze with Tiffany Glass Shades
70053-4	(4) 100W Med.	44"	18"	14"	28 lbs.	Tiffany Bronze with Tiffany Glass Shade
70083-4	(4) 100W Med.	44"	18"	14"	28 lbs.	Tiffany Bronze with Tiffany Glass Shade
70113-4	(4) 100W Med.	44"	18"	14"	28 lbs.	Tiffany Bronze with Tiffany Glass Shade

All fixtures have 3 ft. of chain and 12 ft. of wire.

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
348-VA	(3) 100W Med.	54"	24"	16"	31 lbs.	Vintage Antique with Tiffany Glass Shades
361-VA	(1) 75W Med.	8"	9"	9"	4 lbs.	Vintage Antique, Can be mounted up or down
70023-4	(4) 100W Med.	44"	18"	14"	28 lbs.	Tiffany Bronze with Tiffany Glass Shade
70061-3	(3) 100W Med.	60"	14"	14"	19 lbs.	Tiffany Bronze finish with Mica and Tiffany glass
70064-2	(2) 60W Med.	10"	6"	5"	2 lbs.	Pocket Sconce
770-3-MB-A	(3) 100W Med.	61"	14"	14"	19 lbs.	Mission Bronze finish with Mica and Tiffany glass

All fixtures have 3 ft. of chain and 12 ft. of wire.

Due to its hand-made nature, each piece of tiffany glass will vary slightly in color and pattern.

DESIGNER CLASSICS

The Designer Classics Collection runs the gamut from spirited, fun-loving billiard lights inspired by the game itself..... to an array of stunning, rich designs that make an eye catching statement for any gameroom, bar or kitchen island. Use in any setting where optimal illumination is desired.

190-P-BK-G1



190-1-SN-G1



190-1-BK-G1

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
190-1-BK-G1	(3) 100W Med.	58"	14"	16"	29 lbs.	Matte Black with White Faux-Alabaster Glass Shades
190-1-SN-G1	(3) 100W Med.	58"	14"	16"	29 lbs.	Satin Nickel with White Faux-Alabaster Glass Shades
190-P-BK-G1	(1) 100W Med.	16"	14"	-	9 lbs.	Matte Black with White Faux-Alabaster Glass Shade

All fixtures have 3 ft. of chain and 12 ft. of wire.

*All billiard balls are made from a resin composite, the same as genuine pool balls.



190-1-SN-M



190-1-BK-M


ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
190-1-BK-M	(3) 100W Med.	58"	14"	16"	24 lbs.	Matte Black with Metal Shades
190-1-SN-M	(3) 100W Med.	58"	14"	16"	24 lbs.	Satin Nickel with Metal Shades

All fixtures have 3 ft. of chain and 12 ft. of wire.

*All billiard balls are made from a resin composite, the same as genuine pool balls.



194-WD-G6



191-TB



194-WD-G1



Any billiard fixture which has G series glass is fully interchangeable with other G series Glass and can be ordered on a special order basis.



G1 Glass



G6 Glass



182-AC-M2



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
194-WD-G1	(3) 100W Med.	59"	14"	16"	25 lbs.	Wood Patina with White Faux-Alabaster Glass Shades
194-WD-G6	(3) 100W Med.	59"	9"	16"	25 lbs.	Wood Patina with Amber Gratina Glass Shades

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
182-AC-M2	(3) 100W Med.	58"	15"	16"	22 lbs.	Antique Copper with Textured Iron Shades
191-TB	(3) 100W Med.	63"	21"	16"	25 lbs.	Tiffany Bronze with Metal Shades

All fixtures have 3 ft. of chain and 12 ft. of wire.

All fixtures have 3 ft. of chain and 12 ft. of wire.




ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66115-3	(3) 100W Med.	47"	21"	13"	15 lbs.	Polished Nickel finish
66125-3	(3) 100W Med.	47"	21"	13"	15 lbs.	Satin Nickel finish
66135-3	(3) 100W Med.	47"	21"	13"	15 lbs.	Oiled Bronze finish
66145-3	(3) 100W Med.	47"	21"	13"	15 lbs.	Antique Copper finish

* 1-6" and 2-12" extension rods with hang straight included



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66110-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Polished Nickel finish with White Glass
66130-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Oiled Bronze finish with Amber Glass
66215-3*	(3) 100W Med.	47"	21"	13"	24 lbs.	Polished Nickel finish with White Glass
66225-3*	(3) 100W Med.	47"	21"	13"	24 lbs.	Satin Nickel finish with White Glass
66235-3*	(3) 100W Med.	47"	21"	13"	24 lbs.	Oiled Bronze finish with Amber Glass
66245-3*	(3) 100W Med.	47"	21"	13"	24 lbs.	Antique Copper finish with White Glass

* 1-6" and 2-12" extension rods with hang straight included



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66410-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Polished Nickel finish with Cappa Shells
66415-3*	(3) 100W Med.	47"	21"	13"	24 lbs.	Polished Nickel finish with Cappa Shells
66425-3*	(3) 100W Med.	47"	21"	13"	24 lbs.	Satin Nickel finish with Cappa Shells
66430-1	(1) 100W Med.	5"	13"	7"	4 lbs.	Oiled Bronze finish with Cappa Shells
66435-3*	(3) 100W Med.	47"	21"	13"	24 lbs.	Oiled Bronze finish with Cappa Shells
66445-3*	(3) 100W Med.	47"	21"	13"	24 lbs.	Antique Copper finish with Cappa Shells

* 1-6" and 2-12" extension rods with hang straight included



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
66155-3*	(3) 100W Med.	47"	21"	13"	15 lbs.	Polished Nickel finish, Gloss White metal shades
66165-3*	(3) 100W Med.	47"	21"	13"	15 lbs.	Satin Nickel finish, Gloss White metal shades
66175-3	(3) 100W Med.	52"	16"	14"	14 lbs.	Aged Bronze finish with White glass
66190-1	(1) 60W Med.	8"	8"	10"	2 lbs.	Oiled Bronze with Amber Restoration Glass
66195-3	(3) 100W Med.	57"	14"	16"	19 lbs.	Oiled Bronze with Amber Restoration Glass

* 1-6" and 2-12" extension rods with hang straight included

All fixtures have 3 ft. of chain and 12 ft. of wire.



73046-3




63010-2



7640/1

6552/3



63040-2



73045-3



7630/1

6502/3



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
63010-2	(2) 60W Cand.	12"	17"	7"	4 lbs.	Aged Bronze finish, tan linen shades included
63040-2	(2) 60W Cand.	11"	19"	6"	6 lbs.	Aged Bronze finish, white shades
73045-3	(3) 75W Med.	54"	17"	-	9 lbs.	Aged Bronze finish, white shades
73046-3	(3) 100W Med.	54"	19"	-	9 lbs.	Aged Bronze finish, tan linen shades included

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
6502/3	(3) 75W Med.	43"	26-38"	12"	11 lbs.	Satin Nickel finish
6552/3	(3) 75W Med.	43"	26-38"	12"	11 lbs.	Aged Bronze finish
7630/1	(1) 75W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended, Satin Nickel finish
7640/1	(1) 75W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended, Aged Bronze finish

All fixtures have 3 ft. of chain and 12 ft. of wire.



55047/3



168-SN



17640/1



16552/3



65151-3



14040/1



ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
16552/3	(3) 75W Med.	43"	26-38"	12"	11 lbs.	Oil Rubbed Bronze with white glass shades
17640/1	(1) 60W Med.	7"	12"	8"	2 lbs.	G16 1/2 bulbs recommended
55047/3	(3) 100W Med.	59"	16"	14"	18 lbs.	Oil Rubbed Bronze with opal white glass shades

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
168-SN	(3) 150W Med.	51"	15"	14"	10 lbs.	Satin Nickel with Metal Shades
14040/1	(1) 100W Med.	19"	20"	-	7 lbs.	Dark Rust finish, (16) wine glasses included
65151-3	(3) 100W Med.	56"	33-54"	13"	17 lbs.	Oiled Bronze finish with Metal Shades

All fixtures have 3 ft. of chain and 12 ft. of wire.



NOVELTY

Innovative Lighting For All Ages

5082/2



RACECAR

Race around the track with this sleek racecar.



5112/1



SKATEBOARD



5093/3



WILD RIDE

Cruise proudly with this chopper style motorcycle light. Chrome accents, flames, and an actual working headlight highlight this Wild Ride.



5051/1



PROP PLANE

Fly away with this Satin Nickel prop plane, made of satin and clear glass.



5056/3



CHOPPER

Up, up and away with this helicopter in Satin Nickel with satin and clear glass.



5084/1



BI PLANE

Experience the adventure of a ride in this barnstomer of yesteryear. Satin glass with a Walnut finish.



5052/2



CHOO CHOO

Stay on track with this locomotive light with blue and gray wheels included.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
5082/2	(2) 60W Med.	26"	7"	9"	9 lbs.	Satin Nickel finish
5093/3	(2) 60W Cand. (1) 20W MR16 (included)	23"	9"	7"	11 lbs.	Satin Nickel & Polished Chrome finish
5112/1	(1) 60W Med.	24"	6"	5"	3 lbs.	Chrome finish, includes 3' of cable

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
5051/1	(1) 60W Med.	19"	16"	16"	6 lbs.	Satin Nickel finish
5052/2	(2) 60W Med.	23"	16"	7"	9 lbs.	Satin Nickel finish, comes w/ both blue & gray wheels
5056/3	(3) 60W Med.	24"	13"	5"	9 lbs.	Satin Nickel finish
5084/1	(1) 60W Med.	20"	12"	18"	7 lbs.	Walnut finish



5137/1




BASKETBALL

5138/2



HOCKEY RINK



5123/1




SOCCER BALL



5089/3



SPACEMEN



5088/3



NIGHT SKY


Light up the night with this celestial sky.
Satin white glass with stars and moon.





21005/2



21008/2



21007/2




Bottom View

202-CL



CLOUDS

Daydreams will soar to new heights in the company of these fluffy white clouds drifting across a tranquil blue sky.





Bottom View

205-WM



WORLD MAP

Your young explorer will travel the world with this illuminated explorer's map.



Bottom View

200-MN



MOONSHINE

Glow in the dark! Moonshine offers a playful composition by daylight, while soothing your child into a peaceful slumber by night. Glows gently.

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
5123/1	(1) 60W Med.	10"	11"	-	2 lbs.	White finish, includes 6' of cord
5137/1	(1) 60W Cand.	8"	9"	-	3 lbs.	Satin Nickel finish
5138/2	(2) 60W Med.	22"	12"	12"	14 lbs.	White finish, includes 6' of cable
5088/3	(3) 60W Med.	16"	5"	-	5 lbs.	
5089/3	(2) 60W Cand. (1) 60W Med.	16"	10"	-	6 lbs.	Satin Nickel finish

ITEM NO.	BULB	W	H	EXT.	WEIGHT	ADDITIONAL DETAILS
200-MN	(3) 60W Med.	17"	6"	-	6 lbs.	Glows in the dark
202-CL	(3) 60W Med.	17"	6"	-	6 lbs.	
205-WM	(3) 60W Med.	17"	6"	-	6 lbs.	
21002/2	(2) 60W Med.	13"	4"	-	4 lbs.	White finish
21005/2	(2) 60W Med.	13"	4"	-	4 lbs.	White finish
21007/2	(2) 60W Med.	13"	4"	-	4 lbs.	White finish
21008/2	(2) 60W Med.	13"	4"	-	4 lbs.	White finish



OUTDOOR

Ambiance for the Exterior



87041/1



87042/1



87043/1



87040/1



87044/1

LOWELL

The Lowell outdoor collection features an updated design presence with a welcoming cut-corner angular design and clear halophane glass. Made from solid cast aluminum for outdoor longevity, this series is finished in a versatile Matte Black color.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
87040/1	(1) 60W Med.	6"	13"	-	7"	5"	3 lbs.	
87041/1	(1) 100W Med.	7"	17"	-	10"	6"	6 lbs.	
87042/1	(1) 100W Med.	9"	20"	-	10"	7"	8 lbs.	
87043/1	(1) 100W Med.	7"	13"	51"	-	-	5 lbs.	3' of chain
87044/1	(1) 100W Med.	7"	17"	-	-	-	5 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45145/1




45146/1



45147/1



45144/1



45148/1



BIANCA

The Bianca collection exhibits slender lines and curved seeded glass to provide a fresh update to outdoor settings. The glass is carefully curved to match the frame's profile which is finished in Hazelnut Bronze.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45144/1	(1) 60W Med.	6"	13"	-	7"	3"	5 lbs.	Bulb #1099 optional
45145/1	(1) 100W Med.	8"	16"	-	10"	4"	8 lbs.	Bulb #1099 optional
45146/1	(1) 100W Med.	10"	20"	-	12"	4"	15 lbs.	Bulb #1099 optional
45147/1	(1) 100W Med.	8"	14"	52"	-	-	7 lbs.	Bulb #1099 optional, 3' of chain
45148/1	(1) 100W Med.	8"	15"	-	-	-	7 lbs.	Bulb #1099 optional

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45090/1



45092/1



45091/1



42260/1



LED

***Products exceed Title 24 compliance standards**



42261/1



ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45090/1	(1) 100W Med.	5"	14"	-	7"	2"	3 lbs.	
45091/1	(1) 100W Med.	7"	18"	-	8"	2"	7 lbs.	
45092/1	(1) 100W Med.	5"	13"	51"	-	-	4 lbs.	3' of chain

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42260/1	(1) 6W-246 Lumen LED (included)	8"	14"	9"	4"	4 lbs.	
42261/1	(1) 6W-246 Lumen LED (included)	10"	17"	12"	5"	5 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.

MEDITERRANO

The tapering rectangular design of the Meditterano collection provides transitional styling through its clean lines and clear seeded glass. The Charcoal finish allows the series to be utilized in a range of diverse facades.

LAPUENTE

The Lapuente collection combines the latest in transformer-free LED technology with refined mission styling. A cast aluminum frame finished in Matte Black contrasts nicely with water glass that casts a soft, unobtrusive light.



42095/1



42096/2



42395/1



42396/2



45087/1



45085/1



45086/1



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42095/1	(1) 60W Med.	7"	17"	4"	6"	4 lbs.	
42096/2	(2) 60W Med.	9"	22"	5"	9"	7 lbs.	
42395/1	(1) 60W Med.	7"	17"	4"	6"	4 lbs.	
42396/2	(2) 60W Med.	9"	22"	5"	9"	7 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.

TREVOT

The Trevot collection emphasizes a strong geometric design with vertical and horizontal lines surrounding a half cylindrical shape. Finishes include Sunset Silver or Graphite, both with frosted glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45085/1	(1) 100W Med.	6"	12"	-	7"	6"	5 lbs.	
45086/1	(1) 100W Med.	7"	15"	-	8"	7"	7 lbs.	
45087/1	(1) 100W Med.	8"	17"	-	10"	7"	10 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.

CROFTWELL

This series has bold, yet clean styling with a square, opal white blown glass shade and a modern Textured Matte Black finish.



45133/LED



45132/LED



45131/LED



45130/LED



LED

*Products exceed Title 24 compliance standards



43010/1



43020/1



LED

*Products exceed Title 24 compliance standards

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45130/LED	(1) 11W-690 Lumen LED (integrated)	5"	10"	-	5"	-	3 lbs.	3000K, 80 CRI
45131/LED	(1) 11W-690 Lumen LED (integrated)	6"	12"	-	6"	-	4 lbs.	3000K, 80 CRI
45132/LED	(1) 6W-470 Lumen LED (integrated)	10"	5"	-	-	-	3 lbs.	3000K, 80 CRI
45133/LED	(1) 6W-470 Lumen LED (integrated)	14"	5"	-	-	-	4 lbs.	3000K, 80 CRI

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
43010/1	(1) 5W-220 Lumen LED (included)	4"	12"	5"	5"	3 lbs.	Matte Black finish
43020/1	(1) 5W-220 Lumen LED (included)	4"	12"	5"	5"	3 lbs.	Hazelnut Bronze finish

COLBY

The Colby outdoor collection is constructed of cast aluminum with Matte Silver finish and uses integrated LED lighting inside of its white acrylic diffuser.

FREEMPORT

This collection provides energy savings with transformer free LED technology. Made of durable cast aluminum construction, this series is offered in a Hazelnut Bronze finish with amber glass or Matte Black finish with frosted glass.



42142/2



42146/1



42140/1



42141/1



42145/1

SEDONA

Simplicity of craft and form gives the Sedona collection a very attractive look through its minimalist approach. Inspired by the architecture and casual lifestyle of the desert Southwest, this collection features clean lines with recessed edges. Finished in Clay Bronze with caramel glass.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42140/1	(1) 60W Med.	7"	13"	7"	3"	5 lbs.	
42141/1	(1) 60W Med.	9"	16"	8"	3"	7 lbs.	
42142/2	(2) 60W Cand.	11"	20"	10"	3"	12 lbs.	
42145/1	(1) 60W Med.	9"	18"	6"	-	7 lbs.	
42146/1	(1) 60W Cand.	6"	10"	5"	3"	3 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45151/1



45152/1



45153/1



45150/1



45154/1

MORGANVIEW

The Morganview outdoor collection has a clean transitional design with tapered seedy glass and a Hazelnut Bronze finish.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45150/1	(1) 100W Med.	7"	14"	-	8"	11"	4 lbs.	Bulb #1092 optional
45151/1	(1) 100W Med.	9"	17"	-	10"	13"	6 lbs.	Bulb #1092 optional
45152/1	(1) 100W Med.	11"	20"	-	12"	16"	9 lbs.	Bulb #1092 optional
45153/1	(1) 100W Med.	9"	14"	52"	-	-	6 lbs.	Bulb #1092 optional, 3' of chain
45154/1	(1) 100W Med.	9"	18"	-	-	-	5 lbs.	Bulb #1092 optional

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



42102/1



42106/2



42105/1



42103/1



42104/1



42101/1



42100/1



BLACKWELL

Blackwell is one of England's most important surviving houses from the turn of the 20th century and is a superb example of Arts and Crafts movement architecture. This series, with its simple, yet elegant steel frame design embodies the style characteristic of that era with clean lines and finished in Hazelnut Bronze with cream art glass.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42100/1	(1) 100W Med.	8"	16"	9"	8"	7 lbs.	
42101/1	(1) 100W Med.	9"	19"	12"	9"	10 lbs.	
42102/1	(1) 100W Med.	11"	22"	13"	10"	12 lbs.	
42103/1	(1) 100W Med.	11"	18"	-	-	12 lbs.	3' of chain
42104/1	(1) 100W Med.	9"	18"	-	-	9 lbs.	
42105/1	(1) 60W Med.	6"	12"	8"	7"	4 lbs.	
42106/2	(2) 60W Med.	11"	7"	8"	-	8 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



42182/1



42183/1



42184/1



42181/1



42180/1



SAN GABRIEL

During the late 1800's and early 1900's, Missionary padres from Spain created the California Mission style, which was a simplified version of centuries old Spanish architecture. This style was known for its simplicity of form with minimal ornamentation. The San Gabriel collection pays homage to this design philosophy with smooth, architectural lines and a Hazelnut Bronze finish.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42180/1	(1) 100W Med.	7"	12"	7"	3"	4 lbs.	
42181/1	(1) 100W Med.	9"	16"	10"	2"	6 lbs..	
42182/1	(1) 100W Med.	11"	19"	10"	3"	8 lbs.	
42183/1	(1) 100W Med.	11"	18"	-	-	10 lbs.	3' of chain
42184/1	(1) 100W Med.	11"	20"	-	-	8 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



42171/1




42172/1




42173/1




42170/1


KANSO

“Embracing the everyday, unadorned things in life is to embrace truth”. Rarely has any one philosophy had such a clear and defined impact on a garden style as the indelible mark left by Zen on the Japanese garden. Kanso is one of the six basic aesthetic principles embraced by Zen. Simplistic styling, a key tenet of Zen, and cleanliness of form is a repeated motif in Japanese architecture. Constructed of cast aluminum, this series features an Aged Bronze finish with contrasting white glass.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42170/1	(1) 100W Med.	8"	11"	10"	3"	6 lbs.	
42171/1	(1) 100W Med.	10"	13"	11"	3"	9 lbs.	
42172/1	(1) 100W Med.	10"	13"	—	—	9 lbs.	3' of chain
42173/1	(1) 100W Med.	10"	15"	—	—	8 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45012/1




45013/1




45010/1




45011/1




45014/1


NEWLTON

The Newlton collection projects clean styling and historic character that is carried through the design elements of the frame, arm and backplate. The lantern is constructed of solid cast aluminum, finished in Weathered Charcoal for long lasting durability. The seeded amber linen glass portrays a warm ambiance to your outdoor environment.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45010/1	(1) 100W Med.	7"	12"	9"	3"	4 lbs.	
45011/1	(1) 100W Med.	9"	15"	12"	4"	6 lbs.	
45012/1	(1) 100W Med.	11"	17"	14"	4"	9 lbs.	
45013/1	(1) 100W Med.	9"	13"	-	-	5 lbs.	3' of chain
45014/1	(1) 100W Med.	9"	16"	-	-	6 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



LED

*Products exceed Title 24 compliance standards

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
64010-1	(1) 6W-246 Lumen LED (included)	8"	10"	7"	4"	3 lbs.	
64011-1	(1) 6W-246 Lumen LED (included)	9"	12"	9"	4"	5 lbs.	
64013-1	(1) 6W-246 Lumen LED (included)	9"	14"	9"	-	5 lbs.	

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45095/1	(1) 100W Med.	6"	12"	-	7"	6"	4 lbs.	
45096/1	(1) 100W Med.	7"	16"	-	10"	7"	7 lbs.	
45097/1	(1) 100W Med.	9"	18"	-	11"	7"	9 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.

SAN FERNANDO

Using the latest in transformer-free LED technology, the San Fernando collection has Arts and Crafts styling and warmly greets visitors with its refined lines and Hazelnut Bronze finish. The cast aluminum frame consists of a double arching top and a rectangular cage with panels of richly frosted amber glass.

WINONA

The Winona collection's warm, charming elements of amber glass and a Hazelnut Bronze finish is a welcomed addition to an array of exterior facades. The cylindrical design of the glass and metal accoutrements garners attention from every vantage point.



08163-MBG



08160-MBG



Shown with decorative ring (included)



08161-MBG



08169-MBG



08162-MBG



MADISON

A pristine balance between form and function is achieved with this colonial period rejuvenation series. The Matte Black finish has subtle hand applied gold highlights that grace the antique profile of the fixtures. The water glass diffusers lend a touch of additional texture to complete the stylish impact. Use with or without the decorative ring that is provided with the series.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
08160-MBG	(1) 100W Med.	11"	17"	-	-	9 lbs.	3' of chain
08161-MBG	(1) 100W Med.	7"	11"	8"	2"	3 lbs.	Decorative ring included
08162-MBG	(1) 100W Med.	9"	14"	10"	3"	6 lbs.	Decorative ring included
08163-MBG	(1) 100W Med.	11"	18"	12"	3"	8 lbs.	Decorative ring included
08169-MBG	(1) 100W Med.	9"	16"	-	-	6 lbs.	Decorative ring included

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45111/1



45112/1



45113/1



45110/1



45114/1

COSTA MESA

Quality details abound in this mission inspired outdoor series which is crafted from solid cast aluminum, hammered water glass and a Weathered Charcoal finish.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45110/1	(1) 100W Med.	7"	13"	-	10"	3"	3 lbs.	
45111/1	(1) 100W Med.	9"	17"	-	12"	5"	6 lbs.	
45112/1	(1) 100W Med.	11"	20"	-	14"	5"	8 lbs.	
45113/1	(1) 100W Med.	9"	14"	52"	-	-	5 lbs.	3' of chain
45114/1	(1) 100W Med.	9"	20"	-	-	-	5 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



388-AC



381-AC



389-AC



385-AC



389-BK



381-BK



388-BK



385-BK



RUSTICA

Bring storybook flair to an old English, cottage or Spanish revival-style home with the Rustica Collection. Hand-hammered iron and Scavo seedy-glass cylinders characterize this series, which may be ordered in Matte Black with White Scavo glass and Antique Copper with Amber Scavo glass. They may be used in both indoor and outdoor locations.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
381-AC	(1) 75W Med.	8"	14"	9"	8"	7 lbs.	Antique Copper finish
381-BK	(1) 75W Med.	8"	14"	9"	8"	7 lbs.	Matte Black finish
385-AC	(1) 75W Med.	10"	19"	14"	14"	11 lbs.	Antique Copper finish
385-BK	(1) 75W Med.	10"	19"	14"	14"	11 lbs.	Matte Black finish
388-AC	(1) 75W Med.	7"	18"	-	-	7 lbs.	Antique Copper finish
388-BK	(1) 75W Med.	7"	18"	-	-	7 lbs.	Matte Black finish
389-AC	(3) 60W Cand.	12"	26"	-	-	14 lbs.	Antique Copper finish
389-BK	(3) 60W Cand.	12"	26"	-	-	14 lbs.	Matte Black finish

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



87021/1



87022/1



87023/1



87020/1



87024/1

MADAGASCAR

This series, finished in Matte Black, is constructed of solid cast aluminum for excellent outdoor durability. With European influences, the unique ball-shaped cage and warm amber glass make for a striking addition to an outdoor entrance.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
87020/1	(1) 40W Med.	7"	13"	-	9"	9"	2 lbs.	
87021/1	(1) 60W Med.	9"	16"	-	11"	11"	4 lbs.	
87022/1	(1) 100W Med.	11"	19"	-	13"	12"	5 lbs.	
87023/1	(1) 60W Med.	9"	14"	53"	-	-	3 lbs.	3' of chain
87024/1	(1) 60W Med.	9"	16"	-	-	-	3 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



42007/1



42006/1



42005/1



42405/1



42406/1

MARITIME

Whether you live by the sea or are a sailor at heart, these fixtures are ideal for those of the nautical persuasion. Finishes include Hazelnut Bronze with a clear, lightly seeded glass or Graphite with frosted glass.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42005/1	(1) 60W Med.	9"	10"	11"	4"	2 lbs.	Hazelnut Bronze finish
42006/1	(1) 60W Med.	9"	12"	11"	6"	2 lbs.	Hazelnut Bronze finish
42007/1	(1) 60W Med.	9"	10"	-	-	2 lbs.	3' of chain, Hazelnut Bronze finish
42405/1	(1) 60W Med.	9"	10"	11"	4"	2 lbs.	Graphite finish
42406/1	(1) 60W Med.	9"	12"	11"	6"	2 lbs.	Graphite finish

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



42253/2



45041/1



45031/1



45040/1



Weathered Charcoal



45042/1



45030/1



Regal Bronze



45032/1



SEARSPORT

The simple, yet functional design of the Searsport collection features cast aluminum construction finished in Regal Bronze or Weathered Charcoal and a water glass diffuser.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42253/2	(2) 60W Med.	11"	6"	-	-	5 lbs.	
45030/1	(1) 100W Med.	8"	13"	9"	6"	2 lbs.	
45031/1	(1) 100W Med.	8"	10"	-	-	3 lbs.	3' of chain
45032/1	(1) 100W Med.	8"	15"	-	-	3 lbs.	
45040/1	(1) 100W Med.	8"	13"	9"	6"	2 lbs.	
45041/1	(1) 100W Med.	8"	10"	-	-	3 lbs.	3' of chain
45042/1	(1) 100W Med.	8"	15"	-	-	3 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



47011/1



47021/1



46253/1



46250/1



47010/1



47020/1



46251/1



46252/1



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
47010/1	(1) 60W Med.	8"	8"	9"	4"	1 lb.	
47011/1	(1) 60W Med.	8"	9"	-	-	2 lbs.	
47020/1	(1) 60W Med.	8"	8"	9"	4"	1 lb.	
47021/1	(1) 60W Med.	8"	9"	-	-	2 lbs.	

MARINA

The Marina collection features a charming nautical appeal that will illuminate your outdoor space with distinctive style. Finished in Hazelnut Bronze or Matte Silver.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
46250/1	(1) 100W Med.	6"	11"	-	8"	3"	2 lbs.	
46251/1	(1) 100W Med.	7"	13"	-	9"	3"	3 lbs.	
46252/1	(1) 100W Med.	7"	15"	-	-	-	3 lbs.	
46253/1	(1) 100W Med.	7"	13"	51"	-	-	3 lbs.	3' of chain

MEADOWVIEW

The Meadowview outdoor collection has an updated classic styling exemplified by a frosted glass cylinder and a cast aluminum frame in a Matte Black finish.

Brass and Aluminum Construction



66700-1



66702-1



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
66700-1	(1) 60W Med.	9"	12"	10"	2"	2 lbs.	Bulb #1092 optional
66702-1	(1) 60W Med.	9"	14"	14"	7"	3 lbs.	Bulb #1092 optional

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.

INSULATOR GLASS

The Insulator Glass collection was inspired by the glass relics that adorned the top of telegraph lines at the turn of the 20th century. Acting as the centerpiece of this series is the recognizable shape of the glass insulator, made from thick clear glass that is complimented by solid cast hardware designed with an industrial aesthetic. Finished in Brushed Aluminum.



62001-1



62000-1



62002-1



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
62000-1	(1) 100W Med.	12"	15"	13"	10"	4 lbs.	
62001-1	(1) 100W Med.	11"	14"	22"	11"	4 lbs.	
62002-1	(1) 100W Med.	13"	18"	26"	14"	6 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.

STREETSIDE CAFÉ

Capture the charm of an outdoor café lantern. The Matte Black ironwork and heavy seeded blown glass achieves an authentic old world style.



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42284/1	(1) 100W Med.	7"	12"	9"	6"	2 lbs.	
42285/1	(1) 100W Med.	11"	18"	13"	8"	5 lbs.	
42286/1	(1) 100W Med.	11"	16"	-	-	4 lbs.	3' of chain

P O R T S I D E

Years ago, nautical lighting was purpose built to withstand heavy storms and battering winds. Inspired by those nostalgic lighting fixtures, this series has a simple and charming design finished in Matte Black with clear blown glass.



ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
47045/1	(1) 60W Med.	8"	15"	-	9"	4"	3 lbs.	

W E S T P O R T

The Westport outdoor sconce, finished in Weathered Charcoal, features a restoration stepped design with an outward flaring ribbed glass diffuser.



VILLAGE LANTERN

Historic charm is captured in the Village Lantern collection. This series has a clear glass fount inside a Weathered Charcoal finished wire frame. The handle that adorns the top of the fixture captures the authenticity reminiscent of the function these type of lights had years ago.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
47040/1	(1) 60W Med.	6"	13"	-	8"	5"	3 lbs.	
47041/1	(1) 60W Med.	8"	21"	-	-	-	5 lbs.	
47042/1	(1) 60W Med.	8"	17"	-	10"	6"	4 lbs.	
47043/1	(1) 60W Med.	8"	17"	91"	-	-	5 lbs.	3' of chain
47044/1	(1) 60W Med.	9"	18"	-	11"	6"	5 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45105/1	(1) 60W Med.	10"	12"	-	20"	5"	2 lbs.	Bulb #1092 optional

B A R N S I D E

This country barn inspired outdoor sconce extends far from the wall for a wide dispersion of light. Finished in Hazelnut Bronze with a clear glass diffuser pays homage to restoration styling.



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
43016/1	(1) 60W Med.	6"	14"	7"	2"	2 lbs.	
43017/1	(1) 60W Med.	6"	14"	-	-	2 lbs.	3' of chain

F A R M S T E A D

Lanterns have been widely used for portable lighting for hundreds of years until the time electricity reached rural farming areas. Its simple design and function made it one of the most practical and widely used devices in history. This series carries on this historic design style with clear water glass and period authentic Matte Black finish.





ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
62005-1	(1) 60W Med.	7"	15"	10"	8"	5 lbs.	
62006-1	(1) 60W Med.	8"	16"	-	-	4 lbs.	3' of chain
62007-1	(1) 60W Med.	7"	20"	-	-	3 lbs.	



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
27000/1	(1) 100W Med.	9"	21"	10"	10"	5 lbs.	
27001/1	(1) 100W Med.	11"	22"	10"	10"	6 lbs.	
27002/1	(1) 100W Med.	11"	18"	8"	-	6 lbs.	3' of chain
27003/1	(1) 100W Med.	11"	23"	8"	-	5 lbs.	

WIKSHIRE

Reminiscent of turn of the century gas lights, the Wikshire collection is crafted with the same high quality and historical attributes of that period. Crackled blown glass diffuses the light while a Coffee Bronze finish exudes warmth and tradition.

WORTHINGTON

Welcome guests with the charm of a classic lantern. Constructed of solid cast aluminum, this collection has reeded detailing, clear seeded glass, and a Weathered Rust finish.



41999/2



42000/1



42002/3



42001/2



42003/3



42004/2

BURLINGTON JUNCTION

Located on the Eastern shore of Lake Champlain between the Adirondack and Green Mountains, Burlington is charming and idyllic. This series was inspired by this quaint city by the lake that prides itself in the arts. The fine craftsmanship of this collection is evident in the cast aluminum details and scrollwork. Finished in Hazelnut Bronze, this series is available with amber scavo glass.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
41999/2	(2) 60W Med.	12"	6"	-	-	8 lbs.	
42000/1	(1) 60W Med.	7"	18"	10"	6"	5 lbs.	
42001/2	(2) 60W Cand.	9"	23"	12"	8"	8 lbs.	
42002/3	(3) 60W Cand.	11"	28"	15"	10"	13 lbs.	
42003/3	(3) 60W Cand.	11"	24"	-	-	10 lbs.	3' of chain
42004/2	(2) 60W Cand.	9"	22"	-	-	6 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



BARRINGTON GATE

The design of this series draws its inspiration from historic English Manor houses throughout the Southern region. The traditional design of the cast aluminum framework is accentuated with a Hazelnut Bronze finish and designer water glass.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42030/1	(1) 60W Med.	7"	18"	10"	8"	6 lbs.	
42031/2	(2) 60W Cand.	9"	24"	13"	11"	12 lbs.	
42032/3	(3) 60W Cand.	11"	28"	15"	10"	17 lbs.	
42033/3	(3) 60W Cand.	11"	24"	-	-	12 lbs.	3' of chain
42034/2	(2) 60W Cand.	9"	22"	-	-	8 lbs.	
42035/1	(1) 60W Med.	7"	13"	9"	4"	5 lbs.	
42036/1	(1) 60W Med.	5"	10"	7"	3"	3 lbs.	
42037/2	(2) 60W Med.	12"	6"	-	-	8 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



42062/3




42065/1





42060/1




42063/3




42061/2

42064/2


TUSCANY COAST

The seaside resort of Marina di Piestrasanta offers wonderful landscapes in a relaxing atmosphere. This series is a dedication to the refined details that abound throughout this coastal resort. This series is crafted from cast aluminum with a durable Weathered Charcoal finish and clear seeded glass.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
42060/1	(1) 60W Med.	7"	14"	10"	6"	5 lbs.	
42061/2	(2) 60W Cand.	9"	18"	12"	8"	9 lbs.	
42062/3	(3) 60W Cand.	10"	22"	14"	12"	15 lbs.	
42063/3	(3) 60W Cand.	11"	19"	-	-	11 lbs.	3' of chain
42064/2	(2) 60W Cand.	9"	19"	-	-	7 lbs.	
42065/1	(1) 60W Med.	6"	9"	7"	3"	3 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45004/1



45003/1



45000/1



45002/1



45001/1



45005/1



GLENDALE

The beauty of water glass is encased in a Regal Bronze, cast aluminum frame with a decorative top cap that has ribbed detailing which adds to the classic allure. Complete your outdoor presentation with a versatile array of coordinating fixtures in this series for stunning curb appeal.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45000/1	(1) 100W Med.	7"	13"	8"	10"	2 lbs.	
45001/1	(1) 100W Med.	9"	16"	10"	13"	3 lbs.	
45002/1	(1) 100W Med.	7"	14"	7"	8"	2 lbs.	
45003/1	(1) 100W Med.	9"	18"	12"	10"	4 lbs.	
45004/1	(1) 100W Med.	11"	11"	-	-	3 lbs.	
45005/1	(1) 100W Med.	9"	17"	-	-	3 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



22030/1



22031/1



ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
22030/1	(1) 60W Med.	7"	13"	-	8"	4"	3 lbs.	
22031/1	(1) 60W Med.	7"	18"	-	8"	4"	5 lbs.	

RIVERDALE

This outdoor collection is made from solid Brushed Brass for excellent outdoor durability. The clean lined frame supports curved and beveled glass panels, revealing a slender silhouette.



45020/1



45021/2



45022/3



45023/2



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45020/1	(1) 60W Med.	8"	16"	10"	8"	5 lbs.	
45021/2	(2) 60W Cand.	10"	22"	14"	10"	7 lbs.	
45022/3	(3) 60W Cand.	12"	27"	16"	16"	10 lbs.	
45023/2	(2) 60W Cand.	10"	21"	-	-	5 lbs.	

LAFAYETTE

This classic outdoor design incorporates a beautifully detailed backplate and timeless arching arm that holds a flowing, blown water glass body. Constructed of durable cast aluminum and finished in Regal Bronze.



45050/1



45052/1



45051/1

45053/1



45054/1

W E L L I N G T O N P A R K

The Wellington Park collection has a hexagonal shaped design with arching seeded glass panels held by a scrolled cast aluminum frame. A Weathered Charcoal finish enhances its stately character.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45050/1	(1) 100W Med.	8"	14"	9"	8"	4 lbs.	
45051/1	(1) 100W Med.	9"	17"	11"	10"	4 lbs.	
45052/1	(1) 100W Med.	13"	22"	14"	12"	7 lbs.	
45053/1	(1) 100W Med.	9"	19"	-	-	7 lbs.	3' of chain
45054/1	(1) 100W Med.	9"	21"	-	-	3 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



46190/1



5726-C

**SOLID
BRASS**



5727-C

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
46190/1	(1) 100W Med.	9"	15"	-	6"	8"	5 lbs.	

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
5726-C	(2) 60W Cand.	7"	14"	-	5"	8"	4 lbs.	
5727-C	(3) 60W Cand.	8"	25"	-	7"	8"	10 lbs.	

COVINA

This classic outdoor wall mount has an arched top with stepped detail and clear glass panels. The cast aluminum and steel frame is distinguished by a rich Matte Black finish.

PROVINCIAL

Solid brass lanterns in Charcoal finish with water glass.



47053/3



47054/3



47050/2



47052/2



47051/3



FORGED PROVINCIAL

Lantern collection in Charcoal finish with water glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
47050/2	(2) 60W Cand.	7"	14"	-	5"	10"	4 lbs.	
47051/3	(3) 60W Cand.	8"	23"	-	7"	12"	7 lbs.	
47052/2	(2) 60W Cand.	10"	18"	-	6"	10"	6 lbs.	
47053/3	(3) 60W Cand.	13"	22"	-	5"	12"	8 lbs.	
47054/3	(3) 60W Cand.	12"	23"	-	7"	12"	10 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



FORGED BROOKRIDGE

Lantern collection in Charcoal finish with water glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
47100/1	(1) 60W Med.	6"	12"	-	7"	6"	4 lbs.	
47101/2	(2) 60W Cand.	8"	24"	-	10"	14"	9 lbs.	
47102/3	(3) 60W Cand.	10"	30"	-	12"	15"	14 lbs.	
47103/4	(4) 60W Cand.	13"	37"	-	14"	17"	21 lbs.	
47104/3	(3) 60W Cand.	8"	23"	95"	-	-	7 lbs.	3' of chain
47105/3	(3) 60W Cand.	8"	23"	-	-	-	5 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



FORGED LANCASTER

Lantern collection in Charcoal finish with water glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
47061/2	(2) 60W Cand.	10"	18"	-	6"	11"	7 lbs.	
47062/3	(3) 60W Cand.	11"	29"	-	-	-	17 lbs.	
47063/2	(2) 60W Cand.	9"	26"	-	12"	13"	12 lbs.	
47064/3	(3) 60W Cand.	11"	35"	-	14"	17"	20 lbs.	
47065/2	(2) 60W Cand.	7"	22"	-	9"	10"	8 lbs.	
47066/3	(3) 60W Cand.	11"	27"	101"	-	-	16 lbs.	3' of chain

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



47070/2



47073/3



47072/3



47071/2



47075/3



47074/3



FORGED JEFFERSON

Lantern collection in Charcoal finish with water glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
47070/2	(2) 60W Cand.	6"	11"	-	4"	7"	3 lbs.	
47071/2	(2) 60W Cand.	7"	19"	-	6"	13"	5 lbs.	
47072/3	(3) 60W Cand.	9"	22"	-	7"	13"	8 lbs.	
47073/3	(3) 60W Cand.	11"	27"	-	9"	16"	11 lbs.	
47074/3	(3) 60W Cand.	9"	22"	96"	-	-	8 lbs.	3' of chain
47075/3	(3) 60W Cand.	9"	23"	-	-	-	8 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



701-C



702-C



SOLID BRASS



5720-C



5721-C



SOLID BRASS



704-C



706-C



5722-C



5723-C



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
701-C	(2) 40W Cand.	6"	11"	4"	7"	6 lbs.	
702-C	(2) 60W Cand.	7"	18"	6"	12"	9 lbs.	
704-C	(3) 60W Cand.	9"	22"	7"	14"	14 lbs.	
706-C	(3) 60W Cand.	11"	27"	9"	14"	14 lbs.	

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
5720-C	(1) 60W Med.	8"	13"	10"	7"	6 lbs.	
5721-C	(2) 60W Cand.	10"	17"	12"	9"	10 lbs.	
5722-C	(3) 60W Cand.	12"	20"	14"	11"	12 lbs.	
5723-C	(3) 60W Cand.	12"	22"	-	-	15 lbs.	

JEFFERSON

Solid brass lanterns in Charcoal finish with water glass.

LANDINGS

Solid brass lanterns in Charcoal finish with water glass.



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
6710-C	(1) 60W Med.	8"	20"	12"	10"	11 lbs.	
6711-C	(2) 60W Cand.	10"	26"	13"	11"	15 lbs.	
6712-C	(3) 60W Cand.	12"	33"	15"	14"	25 lbs.	

MANOR

Solid brass lanterns in Charcoal finish with water glass.



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
5214-C	(1) 60W Med.	7"	15"	8"	5"	6 lbs.	
5215-C	(2) 60W Cand.	8"	22"	10"	10"	14 lbs.	
5216-C	(3) 60W Cand.	11"	31"	13"	15"	22 lbs.	
5217-C	(3) 60W Cand.	11"	29"	-	-	20 lbs.	

BRISTOL

Solid brass lanterns in Charcoal finish with beveled glass.



8451-E



8454-E



8449-E



8450-E



8453-E

T A O S

Hand forged iron lanterns in Espresso finish with seeded glass.

ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
8449-E	(2) 60W Cand.	6"	19"	10"	11"	10 lbs.	
8450-E	(2) 60W Cand.	8"	21"	12"	11"	13 lbs.	
8451-E	(3) 60W Cand.	10"	26"	13"	13"	19 lbs.	
8453-E	(3) 60W Cand.	10"	23"	-	-	15 lbs.	
8454-E	(3) 60W Cand.	10"	21"	-	-	16 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45082/1



45081/1



45083/1



45080/1



45084/1



ORLEAN

The Orlean collection, finished in Hazelnut Bronze, features a solid cast aluminum design with a carved, detailed backplate and an elegantly scrolled arm. Clear glass sits inside a scrolled motif lantern body.


ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45080/1	(1) 100W Med.	8"	17"	-	11"	8"	5 lbs.	
45081/1	(1) 100W Med.	10"	21"	-	12"	10"	7 lbs.	
45082/1	(1) 100W Med.	12"	24"	-	14"	13"	13 lbs.	
45083/1	(1) 100W Med.	7"	15"	53"	-	-	6 lbs.	3' of chain
45084/1	(1) 100W Med.	8"	21"	-	-	-	4 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45072/1




45071/1




45074/1




45070/1




45073/1




LOGANSPORT

Made from cast aluminum, the Logansport collection has a highly decorative body with a Hazelnut Bronze finish complimented by warm champagne water glass.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45070/1	(1) 100W Med.	8"	18"	-	9"	11"	4 lbs.	
45071/1	(1) 100W Med.	10"	22"	-	11"	13"	5 lbs.	
45072/1	(1) 100W Med.	11"	24"	-	14"	15"	8 lbs.	
45073/1	(1) 100W Med.	9"	21"	-	-	-	4 lbs.	
45074/1	(1) 100W Med.	10"	20"	58"	-	-	4 lbs.	3' of chain

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



45077/3




45076/1




45078/1




45075/1




45079/1




ANISE

Classically inspired, the Anise collection has a solid cast aluminum construction with clear seedy glass and a Textured Matte Black finish. The end of the arm has a soft petal floral design while a draping detail around the glass adds a traditional flair.

ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45075/1	(1) 100W Med.	7"	17"	-	10"	8"	4 lbs.	
45076/1	(1) 100W Med.	10"	22"	-	12"	9"	5 lbs.	
45077/3	(3) 60W Cand.	11"	26"	-	14"	12"	7 lbs.	
45078/1	(1) 100W Med.	9"	16"	56"	-	-	4 lbs.	3' of chain
45079/1	(1) 100W Med.	9"	20"	-	-	-	4 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



5780-CB



5783-CB



ITEM NO.	BULB	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
5780-CB	(2) 60W Med.	12"	24"	13"	16"	14 lbs.	
5783-CB	(4) 60W Cand.	14"	26"	-	-	16 lbs.	

A C A D I A N A

Hand forged iron lanterns in Castle Bronze finish with water glass.



45089/3



ITEM NO.	BULB	W	H	MAX. H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
45089/3	(3) 100W Med.	26"	91"	-	-	-	14 lbs.	Available only as shown

C E N T R A L S Q U A R E

This three light post light will add the feeling of a small European village to your landscape. A Charcoal finish adds antique charm.



43003AGB



43003CB



45102CHRC




43003GH



43003HB



45101CHRC




43003WC



1000-C



1001-C



43001HB



43001WC



45100CHRC



OUTDOOR ACCESSORIES

ITEM NO.	W	H	WEIGHT	ADDITIONAL DETAILS
1000-C	6"	5"	1 lb.	Charcoal
1001-C	6"	10"	1 lb.	Charcoal
43001HB	3"	84"	5 lbs.	Hazelnut Bronze
43001WC	3"	84"	5 lbs.	Weathered Charcoal
43003AGB	6"	3"	1 lb.	Aged Bronze
43003CB	6"	3"	1 lb.	Clay Bronze

ITEM NO.	W	H	WEIGHT	ADDITIONAL DETAILS
43003GH	6"	3"	1 lb.	Graphite
43003HB	6"	3"	1 lb.	Hazelnut Bronze
43003WC	6"	3"	1 lb.	Weathered Charcoal
45100CHRC	10"	73"	5 lbs.	Charcoal finish
45101CHRC	14"	7"	3 lbs.	Charcoal finish
45102CHRC	3"	4"	1 lb.	Charcoal finish



GAS LANTERNS



7909-WP
[Barcode]

7913-WP
[Barcode]

7941-WP
[Barcode]

7915-WP
[Barcode]

7900-WP
[Barcode]

7905-WP
[Barcode]

7907-WP
[Barcode]

7911-WP
[Barcode]

**SOLID
BRASS**

MARYVILLE

Solid brass gas lanterns in Aged Copper finish with matte black accents and tempered glass for safety with a brass control valve for flame adjustment.



**NATURAL
GAS FLAME**

Gas Lanterns are set up for use with natural gas, can be special ordered for use with propane.

ITEM NO.	LIGHT SOURCE	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
7900-WP	Gas nozzle	10"	36"	18"	16"	25 lbs.	
7905-WP	Gas nozzle	14"	27"	10"	10"	12 lbs.	
7907-WP	Gas nozzle	14"	34"	12"	17"	42 lbs.	
7909-WP	Gas nozzle	8"	29"	12"	14"	16 lbs.	
7911-WP	Gas nozzle	8"	36"	10"	21"	42 lbs.	
7913-WP	Gas nozzle	10"	20"	11"	8"	9 lbs.	
7915-WP	Gas nozzle	10"	27"	11"	15"	42 lbs.	
7941-WP	Gas nozzle	9"	17"	7"	7"	15 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



7916-WP


**SOLID
BRASS**

7912-WP


7908-WP




7914-WP




7906-WP




7910-WP


MARYVILLE



**NATURAL
GAS FLAME**

Gas Lanterns are set up for use with natural gas, can be special ordered for use with propane.

ITEM NO.	LIGHT SOURCE	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
7906-WP	Gas nozzle	14"	30"	-	-	42 lbs.	
7908-WP	Gas nozzle	15"	34"	-	-	42 lbs.	
7910-WP	Gas nozzle	8"	32"	-	-	42 lbs.	
7912-WP	Gas nozzle	9"	36"	-	-	42 lbs.	
7914-WP	Gas nozzle	10"	23"	-	-	42 lbs.	
7916-WP	Gas nozzle	11"	27"	-	-	42 lbs.	



SOLID BRASS

GRANDE ISLE

Solid brass gas lanterns in Aged Copper finish with matte black accents and tempered glass for safety with a brass control valve for flame adjustment.



NATURAL GAS FLAME

Gas Lanterns are set up for use with natural gas, can be special ordered for use with propane.

ITEM NO.	LIGHT SOURCE	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
7921-WP	Gas nozzle	15"	23"	16"	10"	42 lbs.	
7923-WP	Gas nozzle	15"	29"	16"	17"	42 lbs.	
7925-WP	Gas nozzle	8"	15"	10"	8"	42 lbs.	
7927-WP	Gas nozzle	8"	27"	10"	15"	42 lbs.	
7929-WP	Gas nozzle	10"	18"	12"	9"	42 lbs.	
7931-WP	Gas nozzle	10"	25"	12"	16"	42 lbs.	
7933-WP	Gas nozzle	14"	24"	16"	11"	42 lbs.	
7935-WP	Gas nozzle	14"	31"	16"	18"	42 lbs.	
7940-WP	Gas nozzle	8"	16"	7"	7"	15 lbs.	

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.



SOLID BRASS



GRANDE ISLE



NATURAL GAS FLAME

Gas Lanterns are set up for use with natural gas, can be special ordered for use with propane.

ITEM NO.	LIGHT SOURCE	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
7922-WP	Gas nozzle	15"	25"	-	-	42 lbs.	
7924-WP	Gas nozzle	16"	30"	-	-	42 lbs.	
7926-WP	Gas nozzle	8"	18"	-	-	42 lbs.	
7928-WP	Gas nozzle	9"	22"	-	-	42 lbs.	
7930-WP	Gas nozzle	10"	22"	-	-	42 lbs.	
7932-WP	Gas nozzle	11"	25"	-	-	42 lbs.	
7934-WP	Gas nozzle	14"	27"	-	-	42 lbs.	
7936-WP	Gas nozzle	15"	31"	-	-	42 lbs.	



7917-WP



7920-WP



NATURAL GAS FLAME



7919-WP



7918-WP



SOLID BRASS



7904-WP



7904-WP Decorative side scroll shown mounted to gas lantern



ITEM NO.	LIGHT SOURCE	W	H	EXT.	HCWO	WEIGHT	ADDITIONAL DETAILS
7917-WP	Gas nozzle	13"	23"	14"	13"	23 lbs.	
7918-WP	Gas nozzle	13"	26"	-	-	42 lbs.	
7919-WP	Gas nozzle	13"	30"	14"	20"	42 lbs.	
7920-WP	Gas nozzle	14"	30"	-	-	21 lbs.	

ITEM NO.	W	WEIGHT	ADDITIONAL DETAILS
7904-WP	52"	12 lbs.	Matte Black

BAYOU



Solid brass gas lanterns in Aged Copper finish with matte black accents and tempered glass for safety with a brass control valve for flame adjustment.

Gas Lanterns are set up for use with natural gas, can be special ordered for use with propane.

HCWO dimension represents the distance from the center of the junction box to the highest point of the fixture.

GAS LANTERN ACCESSORY

Side scroll option available for gas lantern collections.



CLICKPLATES™ will look great in every room in your home. With four finish options and various configurations, just about any application is possible.




CLICKPLATES™

The Customizable Outlet Cover™


Introducing decorative outlet covers customizable to your receptacle configuration. **"We've got you covered"** with the most popular models and finishes. Quality cast metal construction will add a finishing touch to your decor. Available in Antique Brass, Brushed Brass, Antique Platinum, and Aged Bronze finishes.




Insert plates together



"Click" into place



Cover any configuration




Easy installation with unlimited combinations!

CLICKPLATES™
The Customizable Outlet Cover™

B R U S H E D B R A S S



A N T I Q U E B R A S S



A N T I Q U E P L A T I N U M



A G E D B R O N Z E



C L I C K P L A T E S

Each item comes individually packaged with six (6) in each package.

Each item comes individually packaged with six (6) in each package.

CLICKPLATES[™]
The Customizable Outlet Cover[™]



MEDALLIONS

Decorative Elements For The Ceiling

HARRINGTON

ROSS

PENNINGTON



M1023WH



M1024WH



M1018WH



M1018AB



PENNINGTON



M1019WH



M1019AB



M1020WH



M1020AB



ITEM NO.	W	ADDITIONAL DETAILS
M1018AB	18"	Antique Bronze finish
M1018WH	18"	White finish
M1019AB	28"	Antique Bronze finish
M1019WH	28"	White finish
M1020AB	36"	Antique Bronze finish
M1020WH	36"	White finish
M1023WH	27"	White finish
M1024WH	22"	White finish

A C A N T H U S



M1000WH



M1000AB



M A R I E T T A



M1011WH



M1011AB



A P O L L O



M1010



B R I T T A N Y



M1003



C O R I N N A



M1013WH



M1013AB



ITEM NO.	W	ADDITIONAL DETAILS
M1000WH	11"	White finish
M1000AB	11"	Antique Bronze finish
M1010WH	32"	White finish
M1003WH	19"	White finish
M1011WH	33"	White finish
M1011AB	33"	Antique Bronze finish
M1013WH	33"	White finish
M1013AB	33"	Antique Bronze finish

CAMPIONE



M1001WH



M1001AB



FLORAL WREATH



M1006WH



M1006AB



CORINTHIAN



M1005WH



M1005AB



MELON REED



M1009WH



M1009AB



MEDALLIONS

ITEM NO.	W	ADDITIONAL DETAILS
M1001WH	16"	White finish
M1001AB	16"	Antique Bronze finish
M1005WH	22"	White finish
M1005AB	22"	Antique Bronze finish
M1006WH	24"	White finish
M1006AB	24"	Antique Bronze finish
M1009WH	32"	White finish
M1009AB	32"	Antique Bronze finish

BROOKDALE

ENGLISH STUDY



M1008WH



M1008AB



M1002WH



M1002AB



ENGLISH STUDY



M1012WH



M1012AB



M1022WH



M1022AB



ITEM NO.	W	ADDITIONAL DETAILS
M1008WH	30"	White finish
M1008AB	30"	Antique Bronze finish
M1002WH	18"	White finish
M1002AB	18"	Antique Bronze finish
M1012WH	24"	White finish
M1012AB	24"	Antique Bronze finish
M1022WH	32"	White finish
M1022AB	32"	Antique Bronze finish

HILLSPIRE

LAURELDALE



M1007WH



M1007AB



M1004WH



M1004AB



M1017WH



M1017AB



M1014WH



M1014AB

ITEM NO.	W	ADDITIONAL DETAILS
M1007WH	24"	White finish
M1007AB	24"	Antique Bronze finish
M1017WH	51"	White finish
M1017AB	51"	Antique Bronze finish
M1004WH	21"	White finish
M1004AB	21"	Antique Bronze finish
M1014WH	30"	White finish
M1014AB	30"	Antique Bronze finish

Item Number	Page	Item Number	Page	Item Number	Page	Item Number	Page
1023	194	08096-AGB	158	10159/6+3	352	10422/1	594
1058	202	08097-AGB	158	10160/1	346	10423/1	594
1080	218	08098-AGB	161	10162/6	346	10424/1	594
1081	206	08099-AGB	159	10167/6	106	10429/1	387
1087	334	081-TB-01	296	10169/1	603	10431/1	151
1091	259	081-TB-03	285	10172/1	475	10432/1	594
1092	175	081-TB-04	296	10173/3	475	10433/1	594
1093	272	081-TB-07	281	10174/5	475	10434/1	594
1099	175	081-TB-09	296	10192/4	98	10435/1	595
1101	175	081-TB-10	293	10193/6	98	10436/1	595
1102	175	081-TB-12	297	10208/1	607	10437/1	595
1103	175	081-TB-13	291	10220/1	608	10438/1	595
001-AB	381	081-TB-17	297	10222/1COC	610	10440/1	595
001-TS	381	081-TB-19	297	10223/1	610	10441/1	595
002-AB	381	081-TB-21	297	10231/6	106	10442/1	605
002-TS	381	081-TB-28	297	10240/1	599	10445/1	604
010-AC	70	08100-AGB	159	10241/6	106	10450/1	595
035-IA	284	08101-AGB	158	10242/1	590	10451/1	595
071-TB-01	295	08103-AGB	158	10243/1	591	10455/1	619
071-TB-03	284	08160-MBG	722	10245/1	590	10456/1	619
071-TB-04	295	08161-MBG	723	10246/1	619	10457/1	619
071-TB-07	281	08162-MBG	723	10247/1	598	10458/1	619
071-TB-09	295	08163-MBG	722	10248/1	598	10460/1	609
071-TB-10	293	08169-MBG	723	10249/1	598	10464/1	598
071-TB-12	295	1000-C	782	10253/1	608	10465/1	607
071-TB-13	291	1001-C	783	10254/1	609	10466/1	603
071-TB-17	295	10030/1	549	10256/1	608	10467/1	602
071-TB-19	295	10031/2	549	10260/1	347	10474/1	598
071-TB-21	295	10032/3	549	10261/2	347	10476/1	603
071-TB-28	295	10070/1	565	10263/6	347	10477/1	602
078-TB-01	639	10071/2	565	10270/2	384	10480/1	265
078-TB-03	284	10072/3	565	10271/3	384	10481/3	265
078-TB-04	639	10073/1	643	10272/4	384	10482/4	265
078-TB-07	281	10076/1	611	10280/2	385	10483/5	264
078-TB-09	639	10077/1	609	10281/3	385	110-1	615
078-TB-10	293	10079/1RV	611	10282/4	385	110-8R-BL	627
078-TB-12	639	10088/1	667	10291/1	653	11000/2	207
078-TB-13	290	10089/1	611	10292/1	652	11001/1	207
078-TB-17	639	101-1	618	10293/1	652	11055/4	511
078-TB-19	639	10106/1	653	10303/3	467	11200/1	582
078-TB-21	639	10108/1	652	10313/3	467	11201/3	582
078-TB-28	639	10109/1	652	10326/2	107	11210/1	650
079-TB-01	656	10112/1	655	10327/3	107	11218/3	305
079-TB-03	285	10113/2	353	10328/3	107	11220/1	650
079-TB-04	656	10119/3	353	10329/5	107	11225/2	492
079-TB-07	281	10120/3	352	10330/1TB	603	11226/2	491
079-TB-09	656	10121/6	353	10331/1	150	11227/3	491
079-TB-10	293	10122/2	346	10331/3HAMB	622	11228/1	457
079-TB-12	656	10123/6	346	10332/1	591	11229/2	457
079-TB-13	291	10125/5	474	10333/1	598	11230/3	457
079-TB-17	656	10126/2	105	10341/1	619	11233/3	445
079-TB-19	656	10127/3	105	10342/1	619	11237/1	305
079-TB-21	656	10128/3	105	10343/1	619	11264/1	566
079-TB-28	656	10129/5	105	10360/1	105	11265/2	566
080-TB-03	285	10130/5+5+5	104	10370/1	383	11266/3	566
080-TB-07	281	10139/2SLV	515	10371/1	387	11267/4	566
080-TB-10	292	10139/2WHT	515	10380/1	383	11280/1	535
080-TB-13	290	10140/2	515	10392/4	99	11281/2	535
08014-TBH	282	10141/1	605	10393/6	535	11282/3	535
08015-TBH	283	10142/1	605	10411/3	382	11283/4	535
08016-TBH	283	10143/1	603	10412/1	383	11284/2	191
08018-TBH	282	10144/1FS	607	10413/4	382	11285/1	190
08028-CB	662	10147/1	603	10414/1	383	11286/4	190
08030-AB	286	10150/1DR	671	10415/1	383	11287/6	190
08032-BC	289	10150/1PC	671	10416/1	383	11288/6	190
08092-AGB	160	10151/1DR	657	10418/3	387	11360/9	258
08093-AGB	160	10151/1PC	657	10419/1	387	11361/8+6	258
08094-AGB	160	10152/1DR	519	10420/4	386	11365/1	211
08095-AGB	160	10152/1PC	519	10421/1	618	11366/6+3	211

Item Number	Page	Item Number	Page	Item Number	Page	Item Number	Page
11400/1	562	11642/3	576	11785/5+5	187	14260/1	81
11401/2	562	11643/4	576	11790/1	545	14261/1	81
11402/3	562	11650/1	83	11791/2	545	14262/3	81
11415/1	560	11651/2	83	11792/3	545	14270/1	412
11416/2	560	11652/3	83	11793/4	545	14271/1	412
11417/3	560	11653/4	83	11800/1	544	14272/1	412
11430/1	529	11654/2	83	11801/2	544	14273/1	412
11431/2	529	11655/3	82	11802/3	544	14280/1	173
11432/3	529	11656/5	82	11803/4	544	14281/2	173
11436/1	340	11660/1	570	11805/12+6	266	14282/3	173
11437/2	340	11661/2	570	11806/20+6+3	266	14283/4	173
11438/3	340	11662/3	570	11810/2	120	14284/1	172
11440/2	490	11663/4	570	11811/3	120	14285/1	172
11441/2	490	11670/1	571	11820/2	120	14286/2	172
11445/3	490	11671/2	571	11821/3	120	14290/1	168
11450/2	491	11672/3	571	11825/3	61	14291/1	168
11451/2	490	11673/4	571	11826/4	61	14292/3	168
11453/3	43	11680/1	261	11827/5	60	14300/1	166
11463/3	43	11681/2	261	11830/6	436	14301/3	166
11464/2	491	11682/3	261	12002/1	256	14302/3	166
11465/3	489	11683/4	261	12008/1	256	14305/1	165
11475/1	340	11684/1	260	12017/1	256	14306/1	165
11479/1	340	11685/1	260	12023/2	199	14307/1	165
11480/3	492	11686/6	260	12024/5	198	14310/1	167
11481/4	492	11690/2	209	12025/6	199	14311/1	167
11515/1	522	11691/4	209	14000/1+1	225	14312/1	167
11516/2	522	11692/3	208	14003/1	225	1470/1	428
11517/3	522	11693/2	209	14004/1+1	225	1471/2	429
11518/4	522	11694/4	209	14005/5+5	225	1472/3	429
11540/6	228	11695/8	209	14006/8+4+4	224	1474/1	429
11545/9	437	11696/6+3	208	14040/1	689	1475/6	428
11546/16	437	11700/3	307	14050/1	405	1476/6+3	428
11547/19	436	11701/4	307	14051/3	405	1477/1	429
11551/2	228	11702/4	306	14052/6	405	1477/BR-CAR	627
11554/1	228	11705/1	210	14060/1	461	1478/2	429
11560/2	433	11706/1	210	14061/2	461	15015/2	490
11561/6	433	11710/6	193	14062/3	461	15025/2	490
11562/10	433	11711/8	193	14063/6	460	15030/2	301
11563/15	432	11720/6	192	14120/1	410	15031/3	301
11580/1	573	11721/8	192	14121/1	410	15032/4	301
11581/2	573	11725/LED	441	14122/4	410	15033/1	301
11582/3	573	11727/LED	441	14123/6	410	15034/6	301
11583/4	573	11728/LED	441	14130/1	170	15035/5	300
11584/1	191	11729/LED	442	14131/4	170	15036/8+4	300
11585/2	191	11730/LED	442	14134/6	170	15037/8+8+4	300
11586/4	191	11731/LED	442	14190/1	144	15040/2	275
11587/6	191	11750/15	435	14191/1	144	15041/3	275
11590/1	572	11751/19	435	14192/1	144	15042/5	274
11591/2	572	11752/24	435	14200/1	337	15043/6+3	274
11592/3	572	11753/29	435	14201/1	337	15044/12+6	275
11593/4	572	11754/31	434	14202/2	337	15081/3	272
11595/1	355	11760/2	354	14203/5	337	15083/5	272
11596/2	355	11761/3	355	14204/4+4	336	1510/1	663
11597/3	355	11762/1	354	14205/4+4	336	1511/2	492
11598/4	355	11763/3	354	14210/1	59	1513/2	492
11600/1	575	11764/6+3	354	14211/3	59	1515/2	492
11601/2	575	11770/2	240	14212/3+1	59	1520/1	663
11602/3	575	11771/3	241	14213/4+1	58	15900/1	94
11603/4	575	11772/6	241	14214/5+1	58	15901/4	95
11620/1	524	11773/8	238	14240/1	144	15902/5	95
11621/2	524	11774/3	241	14241/1	145	15903/8	94
11622/3	524	11775/5	238	14242/1	144	15904/14	94
11623/4	524	11776/6+3	240	14243/3	145	15974/5	197
11630/1	525	11777/8+4	239	14244/6	145	15975/8	197
11631/2	525	11780/2	186	14250/1	339	15976/1	197
11632/3	525	11781/4	187	14251/3	339	15986/1	197
11633/4	525	11782/5	187	14252/4+4	338	16011/1	464
11640/1	576	11783/5	186	14253/6+5	339	16012/3	464
11641/2	576	11784/7	186	14259/5	164	16050	248

Item Number	Page	Item Number	Page	Item Number	Page	Item Number	Page
1620/2	371	17231/1	126	194-WD-G6	680	22031/1	754
16239/5	200	17232/1	127	1990/3	456	22040/2	319
1624/6	371	17235/1	129	1991/1	456	22041/8	319
16240/8	200	17240/2	127	200-MN	518	2391/1	257
16241/2	201	17241/1	126	20000/1	606	2392/2	257
16242/1	201	17242/1	127	20001/1	612	2395/3	257
16243/4	201	17245/1	129	20005/1	375	2396/5	257
16244/6	201	17248/1	121	20006/5	375	2400/2	206
16245/6	205	17250/2	127	20007/3	374	2402/6	206
16550/1	368	17251/1	126	20008/3	375	2404/6+6	206
16551/2	368	17252/1	127	20009/5	374	2420/1	221
16552/3	368	17255/1	129	20058/2	251	2424/2	220
168-SN	689	17258/1	121	20059/4	251	2425/3	220
17016/1	358	17260/1	563	20061/2	221	2426/1	221
17019/4	360	17261/2	563	20064/1	621	2431/6	220
17020/1	365	17262/3	563	20064/3	622	2434/12	221
17021/2	365	17263/4	563	20075/3	247	245-BK	273
17023/3	365	1743/2	369	20089/3	251	247-BK	273
17024/4	365	17640/1	369	20100/2	491	2490/1	219
17026/1	362	17641/2	369	20101/3	491	2493/4	218
17027/1	362	17642/3	369	20131/3	491	2494/6	219
17029/4	364	17643/4	369	20150/1	370	2495/6	219
17042/1ALM	621	17645/3	367	20151/2	370	2496/6+4	218
17047/1	358	17646/5	367	20152/3	370	2497/6+3+6	219
17050/1	559	17647/5	367	20154/6	370	2500AB	798
17051/2	559	17648/6+3	366	20155/6	370	2500AGB	799
17052/3	559	18093/1	243	20160/12L	469	2500AP	799
17053/1	502	18094/3	243	20160/12R	469	2500BR	798
17054/1	635	18096/3	243	20160/20R	468	2501AB	798
17080/1	550	18111/2	234	20160/4	468	2501AGB	799
17081/2	550	18112/3	234	202-CL	518	2501AP	799
17082/3	550	18113/5	234	205-WM	518	2501BR	798
17083/4	550	18123/1	235	21005/2	518	2502AB	798
17100/1	561	18124/4	235	21007/2	518	2502AGB	799
17101/2	561	18125/5	235	21008/2	518	2502AP	798
17102/3	561	18130/2	233	2150/1	798	2502BR	798
17103/4	561	18132/3	233	2151/2	217	2503AB	798
17130/1	547	18133/1	232	2152/3	217	2503AGB	799
17131/3	547	18134/4	232	2153/4	217	2503AP	799
17132/4	547	18135/5	232	2154/1	216	2503BR	798
17150/1	654	18140/2	236	2155/2	216	2504AB	798
17151/2	668	18141/1	237	2156/2	216	2504AGB	799
17152/1	669	18142/3	236	2157/3	216	2504AP	799
17153/1	654	18143/5	237	2161/6	798	2504BR	798
17154/2	668	18144/3	237	2163/6	798	2505AB	798
17155/2	668	18145/5	237	2164/6+3	215	2505AGB	799
17156/1	669	18147/8+4	236	2165/8+4	214	2505AP	799
17160/1	669	182-AC-M2	681	2166/10+5	214	2505BR	798
17161/2	669	190-1-BK-G1	678	2180/2	227	2506AB	798
17165/1	450	190-1-BK-M	679	2181/3	227	2506AGB	799
17166/3	450	190-1-SN-G1	678	2183/6	226	2506AP	799
17170/1	419	190-1-SN-M	679	2184/6+3	227	2506BR	798
17171/3	419	190-11-TB-T8	676	22000/2	316	2507AB	798
17180/1	528	190-P-BK-G1	678	22001/6	316	2507AGB	799
17181/2	528	19000/1	391	22002/2	317	2507AP	799
17182/3	528	19003/6	391	22003/2	317	2507BR	798
17183/4	528	19030/2	471	22004/4	317	2508AB	798
17190/1	413	19031/1	471	22005/2	315	2508AGB	799
17195/1	423	19033/5	471	22006/3	315	2508AP	799
17196/1	423	19060/2	470	22007/4	315	2508BR	798
17200/1	425	19061/1	470	22011/3	314	251-BK	273
17201/1	424	19063/5	470	22012/4	314	2580/1	602
17205/1	594	19065/3	470	22013/8	314	2581/1	602
17208/1	122	191-TB	681	22016/2	318	2582/1	602
17210/1	425	19100/4	446	22020/1	101	2583/1	602
17211/1	424	19101/4	448	22021/3	101	2595/1	456
17220/1	425	19102/4	447	22025/1	313	26000/2	673
17221/1	424	19103/4	449	22026/3	313	26001/1	673
17230/2	127	194-WD-G1	680	22030/1	754	26004/1	673

Item Number	Page	Item Number	Page	Item Number	Page	Item Number	Page
27000/1	745	31098/6	178	31338/6R-VINW	626	31484/3+3	102
27001/1	745	31100/2	481	31339/1	601	31486/1	620
27002/1	745	31101/3	480	31340/1	422	31487/1	620
27003/1	745	31102/1	481	31341/1	421	31488/1	620
281-OB	79	31103/1	481	31346/1	546	31489/1	620
283-OB	78	31104/4	481	31347/3	546	31495/1	601
286-OB	78	31105/4	480	31348/1MN	604	31500/2	262
289-OB	79	31106/6	480	31360/1	348	31501/6	262
2993/3	456	31108/3	312	31361/2	348	31502/3+3	263
2997/1A	456	31109/3	312	31362/3	348	31503/3	262
30006/13	444	31120/1	377	31363/3	348	31504/3	263
30007/42	444	31121/2	377	31364/5	348	31505/1	97
30008/3	462	31122/3	377	31370/1	349	31506/4	97
30014/7	463	31123/1	377	31371/2	349	31507/4	97
30015/13	454	31127/5	377	31372/3	349	31508/4	97
30020/12	455	31133/1	611	31373/3	349	31509/6	96
30021/13	454	31137/1	609	31374/5	349	31510/1	63
30023/5	454	31138/1	609	31376/1	605	31511/6	63
30024/9	463	31142/1	604	31380/1	598	31512/8	62
30025/15	462	31143/1	599	31381/1AGS	149	31515/3	263
30026/18	463	31147/1	608	31381/1OB	149	31519/3	344
30031/3	465	31148/1	599	31396/3	311	31520/1	650
30032/10	465	31162/1	542	31398/6	311	31523/3	378
30033/10	465	31163/2	542	31415/1	534	31524/5	378
31006/5	335	31164/3	542	31416/3	534	31525/4	379
31007/3	335	31165/4	542	31420/1	108	31529/3	344
31010/1	335	31180/1	523	31421/2	108	31530/1	650
31013/3	334	31181/2	523	31422/3	108	31538/1	609
31014/6	334	31182/3	523	31423/1	108	31539/1CG	601
31018/6	399	31183/4	523	31424/3	108	31540/1	654
31020/2	483	31185/1	324	31426/1	379	31545/12	439
31021/1	483	31186/3	325	31427/2	379	31546/18	438
31022/2	483	31187/4	325	31428/3	379	31547/16	439
31023/4	483	31188/5	324	31429/4	379	31550/1	400
31024/3	482	31210/1	124	31430/1	184	31551/3	401
31025/3	482	31211/2	124	31431/3	185	31554/1	401
31026/5	482	31212/1	124	31432/6	185	31555/3	401
31030/1	308	31213/4	124	31433/8	184	31556/6	400
31031/3	308	31225/6	351	31436/1	533	31565/4	25
31032/1	308	31235/1	21	31437/2	533	31566/5	24
31033/4	308	31236/1	20	31438/3	533	31567/6	24
31035/1	473	31237/6	21	31439/4	533	31570/8	398
31036/1	473	31238/6	21	31442/1	420	31571/12	398
31037/1	473	31239/9	20	31445/1	601	31580/3	458
31038/3	473	31240/2	452	31450/1	372	31581/6	458
31039/5	473	31241/2	452	31451/3	372	31590/3	459
31040/2	476	31242/3	452	31452/4	372	31591/6	459
31041/1	476	31244/4	452	31453/8	372	31600/1	612
31042/3	476	31260/1	343	31455/1	333	31610/1	612
31043/5	476	31261/2	343	31456/3	333	31615/1	601
31044/2	477	31262/3	342	31457/3+3	333	31616/1	601
31045/1	477	31264/3	343	31460/1	373	31617/1	601
31046/3	477	31266/6	342	31461/3	373	31620/1	612
31047/5	477	31284/2	514	31462/4	373	31625/4	472
31048/1	477	31290/1	427	31463/8	373	31630/1	612
31069/1	479	31291/1	427	31465/1	332	31635/4	472
31070/2	479	31292/5	426	31466/3	332	31650/3	341
31072/1	479	31293/5	427	31467/3+3	332	31651/3	341
31073/1	478	31302/1	345	31470/2	329	31658/1	604
31074/3	478	31312/1	345	31472/3	329	31660/3	440
31075/5	478	31330/1	331	31473/3	329	31661/6	440
31076/1	600	31331/1	331	31474/5	328	31668/1	604
31077/1	600	31332/1	331	31475/5	329	31770/2	182
31078/1	600	31333/1	331	31476/10	328	31771/6	183
31078/3L	623	31334/3	331	31477/1	329	31772/1	181
31080/1	597	31335/4	331	31480/1	103	31773/3	180
31095/1	179	31336/4	330	31481/2	103	31774/5	181
31096/4	179	31337/5	330	31482/1	102	31776/6	183
31097/6	179	31338/1VINW	604	31483/5	103	31777/8	183

Item Number	Page	Item Number	Page	Item Number	Page	Item Number	Page
31778/6	181	416-3M	622	43020/1	707	45147/1	701
31779/6+3	180	41999/2	746	44005/6	259	45148/1	701
31780/6	182	42000/1	746	45000/1	753	45150/1	711
31781/8	182	42001/2	747	45001/1	753	45151/1	710
31790/1	24	42002/3	746	45002/1	752	45152/1	710
31791/1	25	42003/3	747	45003/1	752	45153/1	711
31792/1	25	42004/2	747	45004/1	752	45154/1	711
31801/3	269	42005/1	730	45005/1	753	46000/1	597
31802/4	269	42006/1	730	45010/1	719	46000/8R	627
31803/6	269	42007/1	730	45011/1	719	46005/1	594
31804/5	268	42030/1	749	45012/1	718	46007/1	147
31805/5	268	42031/2	748	45013/1	719	46008/1	147
31811/3	271	42032/3	748	45014/1	719	46008/3L	623
31812/4	271	42033/3	749	45020/1	755	46009/1	147
31813/6	271	42034/2	749	45021/2	755	46010/1	597
31814/5	270	42035/1	748	45022/3	755	46014/1	146
31815/5	270	42036/1	749	45023/2	755	46017/1	146
31820/6	64	42037/2	749	45030/1	733	46018/1	146
31821/12	65	42060/1	751	45031/1	733	46019/1	146
3341/2	213	42061/2	751	45032/1	733	46020/1	309
3343/3	212	42062/3	750	45040/1	732	46021/3	309
3344/6	213	42063/3	751	45041/1	732	46022/4	309
3345/8+4	212	42064/2	751	45042/1	732	46023/1	147
348-VA	279	42065/1	750	45050/1	756	46024/1	147
361-VA	280	42095/1	704	45051/1	757	46030/1	670
362-VA	278	42096/2	704	45052/1	756	46031/3	514
363-VA	279	42100/1	713	45053/1	757	46040/2	189
366-VA	278	42101/1	713	45054/1	757	46044/4	189
369-VA	279	42102/1	712	45070/1	777	46045/6	189
381-AC	726	42103/1	713	45071/1	776	46046/3	188
381-BK	727	42104/1	713	45072/1	776	46047/6	188
3820/2	223	42105/1	712	45073/1	777	46048/6+3	188
3821/3	223	42106/2	712	45074/1	777	46049/8+6	189
3822/4	223	42140/1	709	45075/1	779	46060/1	327
3823/1	223	42141/1	709	45076/1	778	46061/3	327
3824/2	222	42142/2	708	45077/3	778	46062/6	327
3825/3	223	42145/1	709	45078/1	779	46063/8	326
3826/5	222	42146/1	709	45079/1	779	46100/2	113
385-AC	726	42170/1	717	45080/1	775	46101/3	113
385-BK	727	42171/1	716	45081/1	774	46102/2	112
388-AC	726	42172/1	717	45082/1	774	46103/3	112
388-BK	727	42173/1	717	45083/1	775	46104/3	113
389-AC	726	42180/1	715	45084/1	775	46105/3	112
389-BK	727	42181/1	715	45085/1	705	46107/1	599
3L-CHR	623	42182/1	714	45086/1	705	46110/2	117
3L-OB	623	42183/1	715	45087/1	705	46111/3	117
3L-SN	623	42184/1	715	45089/3	781	46112/2	116
3T-CHR	622	42253/2	732	45090/1	702	46113/3	116
3T-OB	622	42260/1	703	45091/1	702	46114/3	117
3T-SN	622	42261/1	703	45092/1	702	46115/3	116
4000/2	254	42284/1	738	45095/1	721	46120/2	111
4001/3	254	42285/1	738	45096/1	721	46121/3	111
4002/5	254	42286/1	738	45097/1	721	46122/2	110
4003/6+3	254	42395/1	704	45100CHRC	783	46123/3	110
4010/2	255	42396/2	704	45101CHRC	783	46124/3	111
4011/3	255	42405/1	731	45102CHRC	783	46125/3	110
4012/5	255	42406/1	731	45105/1	742	46130/2	115
4013/6+3	255	426-1M	667	45110/1	725	46131/3	115
4021/1	256	426-1WS	667	45111/1	724	46132/2	114
4040/3	256	43001HB	783	45112/1	724	46133/3	114
4041/3	256	43001WC	783	45113/1	725	46134/3	115
4050/2	252	43003AGB	782	45114/1	725	46135/3	114
4051/1	253	43003CB	782	45130/LED	706	46156/1	548
4052/3	253	43003GH	782	45131/LED	706	46157/2	548
4053/3	253	43003HB	782	45132/LED	706	46158/3	548
4054/5	252	43003WC	782	45133/LED	706	46161/1	599
406-1	616	43010/1	701	45144/1	701	46162/1	599
413-AS	256	43016/1	743	45145/1	700	46170/1	597
416-1	614	43017/1	743	45146/1	700	46171/1	597

Item Number	Page	Item Number	Page	Item Number	Page	Item Number	Page
46172/1	597	5123/1	644	570-4N-SW	581	61030-2	350
46180/1	620	5137/1	644	57000/LED	499	61031-3	350
46181/1	620	5138/2	694	57001/LED	499	61032-5	350
46182/1	620	517-1	613	57010/LED	499	61040-1	670
46185/3	453	52000/1	568	57011/LED	499	611-CB	292
46190/1	758	52001/2	568	57020/LED	499	614-CB	292
46200/1	414	52002/3	568	57021/LED	499	62000-1	737
46201/1	414	52003/4	568	57025/2	376	62001-1	737
46202/1	414	52010/1	569	57026/1	376	62002-1	737
46203/1	414	52011/2	569	57027/4	376	62005-1	744
46210/1	415	52012/3	569	57030/1	29	62006-1	744
46211/1	415	52013/4	569	57031/1	27	62007-1	744
46212/1	415	5214-C	771	57032/1	28	621-AB	286
46213/1	415	5215-C	771	57040/1	29	622-AB	286
46220/1	148	5216-C	771	57041/1	27	6230/2	203
46221/1	148	5217-C	771	57042/1	28	6231/1	204
46222/1	148	522-1	613	57050/1	29	6232/4	204
46230/12	75	527-1	610	57051/1	27	6233/6	205
46231/12	75	528-1	605	57052/1	28	6234/6	205
46232/24	74	528-3L-SLV	623	57060/1	29	6235/4	204
46250/1	735	53000/1	466	57061/1	27	6236/6	203
46251/1	735	53001/3	466	57062/1	28	6237/6+3	202
46252/1	735	53002/1	466	57080/1	29	6238/2	204
46253/1	735	54000/1	541	57081/1	26	6242/4	493
47010/1	734	54001/2	541	57082/1	28	629-AB	287
47011/1	734	54002/3	541	57090/1	407	63010-2	90
47020/1	734	54003/4	541	57091/4	407	63011-2	90
47021/1	734	54010/1	417	57092/4+4	406	63012-1	90
47040/1	741	54011/2	417	57093/5	407	63013-3	91
47041/1	741	54012/3	417	57094/8	407	63014-4	91
47042/1	741	54013/4	416	5720-C	769	63015-5	88
47043/1	741	54014/1	417	5721-C	769	63016-6	90
47044/1	740	54015/3	417	5722-C	769	63017-8	89
47045/1	739	54016/4	416	5723-C	769	63018-6	93
47050/2	761	54017/6	416	5726-C	759	63019-6	89
47051/3	761	54018/1	416	5727-C	759	63020-1	125
47052/2	761	542-1	604	5780-CB	780	63021-2	125
47053/3	760	544-1MO	611	5783-CB	780	63022-1	125
47054/3	760	544-6R-MO	626	5960/1	195	63023-4	125
47061/2	764	545-1SAH	602	5962/3	195	63024-1	80
47062/3	765	546-1	607	5963/6	195	63025-1	80
47063/2	764	55000/1	123	5964/3	195	63034-1	80
47064/3	764	55001/1	123	5965/4	196	63035-1	80
47065/2	765	55002/3	123	5967/6+4	194	63040-2	92
47066/3	765	55003/4	123	5970/2	195	63041-5	93
47070/2	766	55005/6	672	5972/1	196	63042-6	92
47071/2	767	55010/1	57	5973/4+1	196	63043-8	92
47072/3	766	55011/1	56	60004-1	128	63050-1	87
47073/3	766	55020/1	57	60005-1	128	63051-2	87
47074/3	767	55021/1	56	60014-1	128	63052-2	86
47075/3	767	55030/1	57	60015-1	128	63053-1	86
47100/1	762	55031/1	56	60016-2	664	63054-3	86
47101/2	763	55040/1	57	60018-1	640	63055-6	84
47102/3	763	55041/1	56	60042-1	140	63056-5	84
47103/4	762	55045/1	73	60043-1	140	63057-6	87
47104/3	762	55046/2	73	60044-1	141	63058-8	85
47105/3	763	55047/3	72	60044-6R	626	63060-1	91
50003/LED	418	551-1	603	60045-1	141	63070/1	323
501-1	617	570-1B-C	580	60046-1	140	63071/2	323
502-1	617	570-1C-WS	581	60047-1	140	63073/3	323
5051/1	693	570-1N-SW	581	60052-1	142	63074/5	323
5052/2	693	570-2B-C	580	60053-1	142	63075/12	322
5056/3	693	570-2C-WS	581	60054-1	143	640-BC	288
5082/2	692	570-2N-SW	581	60055-1	143	64010-1	720
5084/1	693	570-3B-C	580	60056-1	142	64011-1	720
5088/3	497	570-3C-WS	581	60057-1	142	64013-1	720
5089/3	694	570-3N-SW	581	60064-1	143	641-BC	288
5093/3	692	570-4B-C	580	60065-1	143	648-BC	289
5112/1	692	570-4C-WS	581	60066-1	141	6500/1	358

Item Number	Page	Item Number	Page	Item Number	Page	Item Number	Page
65004-1	171	66180-1	53	66431-2	47	66890/1	23
65006-1	171	66181-1	55	66432-1	46	66891/1	22
65007-5	171	66182-3	54	66433-1	39	66892/1	23
6501/2	359	66183-5	53	66435-3	51	66893/4	23
6502/3	359	66185/1	551	66441-2	47	66894/6	22
65049-1	70	66186/2	551	66442-1	46	66910/4	76
65051-1	71	66187/3	551	66443-1	39	66911/6	76
65060-1	69	66188/4	551	66445-3	51	66912/10	77
65061-1	68	66190-1	163	66460/1	267	66920/2	304
65070-1	69	66191-3	163	66513-1	37	66921/8	304
65071-1	68	66194-1	162	66514-1	40	66930/1	403
65072-1	70	66195-3	163	66515-1	40	66931/4	403
65073-1	70	66196-3	162	66516-1	40	66940/1	402
65080-1	69	66197-5	162	66523-1	37	66941/4	402
65081-1	68	66210-1	152	66524-1	40	66945/1	169
65090-1	69	66211-1	153	66525-1	40	66950/1	404
65150-2	66	66212-2	153	66526-1	40	66951/3	404
65151-3	67	66213-3	153	66533-1	37	66955/1	169
6550/1	362	66214-4	153	66543-1	37	67010-1	579
6551/2	363	66215-3	50	66630-1	45	67011-2	579
6552/3	363	66216-1	152	66631-2	45	67012-3	579
66092-3	161	66217-1	152	66632-1	44	67020-1	578
66093-4	161	66221-1	152	66633-1	38	67021-2	578
66110-1	45	66225-3	50	66635-3	50	67022-3	578
66111-2	45	66234-1	503	66670-1	53	67040/1	133
66112-1	44	66235-3	50	66671-1	55	67041/1	133
66113-1	38	66245-3	50	66672-3	54	67042/1	133
66114-1	34	66250-1+1	670	66673-5	52	67045/1	132
66115-3	48	66254-2	736	66700-1	132	67046/1	132
66118-1	35	66265-3	174	66702-1	736	67051/1	133
66119-1	42	66280-2	100	66751-1	43	67056/1	132
66120-3	42	66282-6	100	66760-1	43	67060/1	134
66121-2	45	66310-3	310	66761-1	43	67061/1	134
66122-1	44	66311-3	310	66771-1	43	67062/1	134
66123-1	38	66315/1	118	66780-1	43	67063/1	134
66124-1	34	66316/1	118	66781-1	43	67066/1	132
66125-3	48	66317/1	118	66800-1	136	6710-C	770
66128-1	35	66322-4	157	66810-1	138	6711-C	770
66130-1	45	66323-4	157	66812-1	138	6712-C	770
66131-2	45	66325/1	118	66813-1	138	67712-1	41
66132-1	44	66326/1	118	66815-1	138	67713-1	36
66133-1	38	66335-3	161	66816-1	138	67722-1	41
66134-1	34	66345/1	130	66817-1	139	67723-1	36
66135-3	48	66346/1	131	66818-1	139	67732-1	41
66138-1	35	66350/1	119	66820-1	136	67733-1	36
66139-1	42	66351/1	119	66822-1	136	67742-1	41
66141-2	45	66355/1	130	66823-1	136	67743-1	36
66142-1	44	66356/1	131	66825-1	136	69029-1	155
66143-1	38	66360/1	119	66826-1	136	69039-1	155
66144-1	34	66361/1	119	66827-1	137	69040-1	154
66145-3	49	66365/1	130	66828-1	137	69042-1	155
66148-1	35	66366/1	131	66833-1	137	69043-1	154
66149-1	42	66370/1	135	66843-1	139	69044/1	156
66150-1	53	66371/1	135	66850/1	30	69045/1	156
66151-1	55	66375/1	130	66851/1	32	69050-1	154
66152-3	54	66376/1	131	66852/1	31	69052-1	155
66153-5	52	66380/3	511	66853/1	33	69053-1	154
66155-3	49	66410-1	47	66860/1	30	69054/1	156
66159-1	42	66411-2	47	66861/1	32	69055/1	156
66160-1	53	66412-1	46	66862/1	31	6H-OB	625
66161-1	55	66413-1	39	66863/1	33	6H-SN	625
66162-3	54	66415-3	51	66870/1	30	6R-CHR	626
66163-5	52	66418/2	109	66871/1	32	6R-OB	626
66165-3	49	66419/3	109	66872/1	31	6R-SN	626
66170-1	53	66421-2	47	66873/1	33	6RC-CHR	624
66171-1	55	66422-1	46	66880/1	30	6RC-OB	624
66172-3	54	66423-1	39	66881/1	32	6RC-SN	624
66173-5	53	66425-3	51	66882/1	31	70000-1CW	640
66175-3	685	66430-1	47	66883/1	33	70000-1HB	640

Item Number	Page	Item Number	Page	Item Number	Page	Item Number	Page
70000-1HR	640	7636/5	357	81070/1	539	997-AW-12	510
70007-2	494	7637/5	357	81072/3	539	997-AW-13	291
70014-3	494	7638/6+3	356	81080/3	498	997-AW-17	510
70021-1	278	7640/1	364	81081/4	498	997-AW-19	510
70023-4	280	7641/2	364	82030/6	443	997-AW-21	510
70027-2	494	7642/3	364	83000/3	451	997-AW-28	510
70044-2	390	7643/2	364	83001/6	451	999-1	294
70046-1	390	7644/1	362	8449-E	773	999-10	292
70048-4	390	7645/3	361	8450-E	773	999-12	294
70053-4	676	7646/5	361	8451-E	772	999-13	290
70061-3	303	7647/5	361	8453-E	773	999-17	294
70064-2	303	7648/6+3	361	8454-E	773	999-19	294
70065-2	302	770-3-MB-A	677	85001	245	999-21	294
70066-1	303	7900-WP	786	85002	244	999-28	294
70067-3	302	7904-WP	795	85003	244	999-3	284
70083-4	676	7905-WP	786	85004	245	999-4	294
70089-1	288	7906-WP	789	86051	249	999-7	281
70098-2	283	7907-WP	787	86052	249	999-9	294
701-C	768	7908-WP	788	86053	249	D1812	259
70113-4	287	7909-WP	786	86054	248	D1849	302
70114-1	283	7910-WP	789	87020/1	729	D1852	287
70165-2	289	7911-WP	787	87021/1	728	D2252	71
702-C	768	7912-WP	788	87022/1	728	D2254	71
704-C	768	7913-WP	786	87023/1	729	G1 GLASS	680
7040/2	247	7914-WP	789	87024/1	729	G6 GLASS	680
7042/3	247	7915-WP	787	87040/1	699	LA100	645
7043/2	246	7916-WP	788	87041/1	698	M1000AB	804
7044/3	244	7917-WP	794	87042/1	698	M1000WH	804
7046/3	246	7918-WP	794	87043/1	699	M1001AB	806
7047/6	246	7919-WP	794	87044/1	699	M1001WH	806
7050/1	247	7920-WP	794	8820/8	393	M1002AB	809
706-C	768	7921-WP	790	8884/2	394	M1002WH	809
715-TB	290	7922-WP	793	8887/6	394	M1003	804
72000-2	380	7923-WP	791	8888/8	394	M1004AB	811
72001-1	380	7924-WP	792	8889/2	394	M1004WH	811
72003-3	380	7925-WP	790	8894/2	665	M1005AB	806
72021-1	411	7926-WP	793	8R-CHR	627	M1005WH	806
72022-3	411	7927-WP	791	8R-OB	627	M1006AB	807
72060-2	409	7928-WP	792	8R-SN	627	M1006WH	807
72061-2	409	7929-WP	790	9003/2	395	M1007AB	810
72062-1	409	7930-WP	793	9010/9	395	M1007WH	810
72063-4	409	7931-WP	791	9025/6	392	M1008AB	808
72070-2	408	7932-WP	792	9105/4	250	M1008WH	808
72071-2	408	7933-WP	790	9107/4+2	250	M1009AB	807
72072-1	408	7934-WP	793	9108/6+3	250	M1009WH	807
72073-4	408	7935-WP	791	931-VA	281	M1010	804
72077-1	299	7936-WP	792	9319/2	277	M1011AB	805
72078-1	299	7940-WP	790	9320/1	277	M1011WH	805
72079-3	299	7941-WP	787	9321/2	277	M1012AB	808
72080-1	298	7953/2	229	9322/3	277	M1012WH	808
72081-1	298	7956/5	229	9325/1	277	M1013AB	805
73011-1	389	7958/6	229	9326/3	277	M1013WH	805
73020-2	388	7959/8+4	229	9327/5	277	M1014AB	811
73021-1	388	8050/3	230	9328/5	276	M1014WH	811
73022-3	388	8053/5	230	9329/6+3	276	M1017AB	810
73023-5	388	8054/5	231	933-TB	290	M1017WH	810
73030-2	389	8055/8+4	231	9330/6+6+3	276	M1018AB	803
73031-1	389	8056/10+5	230	934-CB	292	M1018WH	803
73032-3	389	8058/3	231	936-CB	509	M1019AB	802
73033-5	389	8059/2	233	937-CB	509	M1019WH	802
73041-1	388	8069/2	233	941-TB	280	M1020AB	803
73045-3	93	8090/2	242	990-D	280	M1020WH	803
73046-3	88	8091/3	242	990-J	289	M1022AB	809
7630/1	360	8092/6	242	997-AW-01	510	M1022WH	809
7631/2	360	81030/1	538	997-AW-03	285	M1023WH	802
7632/3	360	81031/2	538	997-AW-04	510	M1024WH	802
7633/2	360	81032/3	538	997-AW-07	281	ROD KIT-CHR	625
7634/1	358	81040/3	498	997-AW-09	510	ROD KIT-OB	625
7635/3	357	81041/4	498	997-AW-10	293	ROD KIT-SN	625



LAZY SUSAN

lazysusanusa.com

A PURE CELEBRATION OF STYLE

Discover the beauty of nature and the elegance of modern design. Extraordinary design and superior craftsmanship create an enchanting collection of home accessories.



DIMOND

dimondlighting.com

PORTABLE TABLE AND FLOOR LAMPS

Inspired by poetry of light and acclaimed for the elegance with which they are executed, Dimond table and floor lamps transcend the boundaries of innovations and style.



Sterling

mysterlinghome.com

ACCENT FURNITURE, WALL DECOR & ACCESSORIES

Distinctive, innovative & design-driven home furnishings and accessories that uncover styles of the future, while revitalizing themes from the past.



ELK

LIGHTING CREATIVITY™
elklighting.com

LIGHTING FIXTURES

Lighting fixtures for discerning customers that inspire creativity and reflect a commitment to quality, innovation and style.



Alico

alicolighting.com

LED LIGHTING

With over 50 years of experience and passion creating sophisticated lighting fixtures. We are inspired by the latest in design and technology to conceive functional and premium quality products.



CORNERSTONE

cornerstonelighting.com

CONTRACT LIGHTING

A compact, yet versatile and stylish range of lighting designed with the builder and specifier in mind that allows mix and match capabilities across collections.



GUILD MASTER

guildmaster.com

HANDMADE FURNITURE

For over 30 years, the GuildMaster brand has represented the finest in handmade accent furniture. Crafted in solid mahogany using Old World techniques, each piece is truly one of a kind.



MIRROR MASTERS

themirrormasters.com

DECORATIVE MIRRORS

Mirror Masters Company is proud to support many of the most prestigious home furnishing retailers with our products and services, as well as many of the top hospitality projects around the globe.



ELK

HOSPITALITY
elkhospitality.com

HOSPITALITY INDUSTRY

ELK Hospitality offers a full range of styles across multiple product categories including lighting fixtures, lamps, furniture, wall décor and decorative accessories.

COORDINATE YOUR DECOR WITH ELK BRANDS
WHOLE HOME SOLUTIONS

ELK
GROUP INTERNATIONAL

12 Willow Lane / Nesquehoning, PA 18240 / Tel: 800-613-3261 / Fax: 866-613-3264

www.elkgrouppinternational.com / sales@elkgrouppinternational.com

Permanent Showrooms

Atlanta / Dallas / High Point / Las Vegas / New York / Hong Kong / Toronto

Design Studio

12 West 32nd Street, 11th floor / New York, NY 10001